

Declaration of Conformity

According to ISO/IEC 17050-1: 2010

Manufacturer Name: National Instruments
Address: 11500 North MoPac Expressway
Austin, Texas, 78759 USA
Web: www.ni.com/certification

We hereby declare under our sole responsibility that the following apparatus:

Product Description: CABLES, ACCESSORIES, & PERIPHERALS
Model Number(s): SEE LIST IN TABLE STARTING ON PAGE 2
Product Category: SEE LIST IN TABLE STARTING ON PAGE 2

Complies with the essential requirements of the following applicable European Directives:

RoHS Directive 2011/65/EU

Conformity is assessed in accordance to the following standards:

Environmental Affairs: Articles manufactured on or after the Date of Issue of this Declaration of Conformity do not contain any of the restricted substances in concentrations/applications not permitted by the RoHS Directive.

October 11, 2019, Austin, Texas USA

Date and Place of Issue



Dany Cheij, Global Product & Trade Compliance Manager

Table 1 – RoHS-Compliant Cables, Accessories, & Peripherals

Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxxX-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
130343A-01	189864B-01	ACCESSORY KIT, PXIE-1084 TIMING AND SYNC
142947-01	142947B-01	CABLE ASSEMBLY, SHDB62M-DB62M-LL, LOW LEAKAGE, 1M
143078-0250	143078A-0250	CABLE ASSY, SMP CATCHERS MITT PLUG TO SMP BULKHEAD MOUNT, .047 COAX, 250 MM, PACK OF 4
143078-02501	143078A-0250	CABLE ASSY, SMP CATHERS MITT PLUG TO SMP BULKHEAD MOUNT, .047 COAX, 250 MM
143555-0R5	143555A-0R5	USB CABLE WITH RETENTION, TYPE-C MALE TO TYPE-A FEMALE, USB 3.1 GEN 1, 3A, 0.5M
143556-0R5	143556A-0R5	USB CABLE WITH RETENTION, TYPE-C MALE TO TYPE-C MALE, USB 3.1 GEN 1, 3A, 0.3M
144756-32	144756A-32 (rev A or higher)	CABLE ASSY, 2X 36-POS GP POGO PIN BLOCKS TO 160 POS DIN, TYPE GP36/2-DIN160, 32IN
144756-40	144756A-40 (rev A or higher)	CABLE ASSY, 2X 36-POS GP POGO PIN BLOCKS TO 160 POS DIN, TYPE GP36/2-DIN160, 40IN
146561-27	146561A-27	CABLE ASSY, STS GEN2 SYSTEM, 36-POS GP POGO PIN BLOCK TO DB25 + PS + DMM, 27IN
147746-01	147746A-01	CABLE, BREAKOUT, QSFP TO SMA
147789-27	147789A-27	STS M2, CX, SYSTEM CABLE ASSEMBLY, STS-M2-CX-SYS
148795-32	148795A-32	RCB600 POGO CABLE, 36-POS POGO PIN BLOCK TO WIRE FERRULE, NO REMOTE SENSE, 32 IN
148795A-32	148795A-32	CABLE ASSY, 36-POS POGO PIN BLOCK TO WIRE FERRULE, RCB600, NO REMOTE SENSE, 32 IN
148876-12	148876A-12	CABLE GLAND REPLACEMENT PACK, M16 THREAD, QUANTITY 12
148877-01	148877A-01	CABLE GLAND REPLACEMENT, PG16 THREAD, QUANTITY 1
148977-01	148903A-01 754309-01	REPLACEMENT 2.4 GHZ OMNI-DIRECTIONAL ANTENNA, STRAIGHT, 1.5 DBI, RP-SMA, WITH BOOT
149055-0R2	149055A-0R2	CHASSIS TRIGGER BREAKOUT CABLE FOR REM, .2M
151672-4R5	151672A-4R5 (rev A or higher)	CABLE ASSY, 1394A TO 1394B JACKSCREW, BLACK CABLE, 4.5 M
151733-XX	151733A-XX	Cable Assy, CAT-5E Ethernet, Thin Profile, 2M, 5M, and 10 M
152058-0R5	152058A-0R5	FC/APC (Wide Key) To LC/APC Singlemode 0.5M Fiber Optic Adapter Cable
152166-02	152166A-02 (rev A or higher)	USB EXTENSTION WITH RETENTION, TYPE A PLUG AND RECEPTICAL CONNECTORS (2M)
152166-0R5	152166A-0R5 (rev A or higher)	USB EXTENSTION WITH RETENTION, TYPE A PLUG AND RECEPTICAL CONNECTORS (.5M)
152403-4R5	152403A-4R5	CABLE ASSY, 1394B JACKSCREW TO 1394B JACKSCREW, BLACK, 4.5 METER
152580-0R25	152580A-0R25	Flying Lead Cable for USB-8452 - 40 PIN
152629-01	152629A-01	SHH19-H19-Aux Shielded Single Ended Cable for Aux Digital I/O with Jackscrew, 1M
152629-02	152629A-02	SHH19-H19-Aux Shielded Single Ended Cable for Aux Digital I/O with Jackscrew, 2M
152637-01	152637A-01	CABLE, SEMI-RIGID, 5624-5653-5606, CLK-IN TO LO2 OUT
152870-01	152870A-01	SHC68-C68-D4 Shielded Single Ended Cable for High-Speed Digital I/O, Low Leakage, 1M
153108-03	153108A-03	NI 9502 to AKM Motor Power and Feedback Cable Bundle
153166-12	743097-01 152731A-01	9.65MM STANDOFF (QTY 12)
153170-01	153170C-01L	NI 9693 2-Slot C Series RMC
153901-01	153585A-01 153910A-01	NI 9695 Thermal Kit
153901-02	153901A-02	THERMAL KIT FOR SBRIO-9607/9627/9637
154041-01	154041a-12	NI sbRIO 50 PIN Ribbon Cable with IDC Headers
154066-02	154066E-02L	HS/FD CAN EXTERNAL TRANCEIVER CABLE_SPLIT SDA
154081-02	154081B-02L	LIN EXTERNAL TRANCEIVER CABLE_SPLIT SDA
154302-01	154302A-01	Low Profile I/O Cable, 37-PIN Female DSUB to Male DSUB (1M)
154454-01	154454B-01	MSO LOGIC ANALYZER 40 PIN INPUT CABLE
154752-01	154752A-01 (rev A or higher)	9.65MM STANDOFFS AND SCREWS FOR SBRIO RMC (4X STANDOFF: 4-40 X 0.380 IN, 8X SCREWS: 4-40 X 1/4 IN)
155475-03	155475A-03 (rev A or higher)	CABLE, 26-PIN D-SUB MALE TO PIGTAIL, 3M
156083-03	156083A-03 (rev A or higher)	44-PIN HDSUB MALE TO PIGTAIL, 3 METER CABLE
156084-03	156084A-03 (rev A or higher)	44-PIN HDSUB MALE TO 44-PIN HDSUB FEMALE 3 METER CABLE
156084-0R5	156084A-0R5 (rev A or higher)	44-PIN HDSUB MALE TO 44-PIN HDSUB FEMALE .5 METER CABLE
156166-01	156166A-01	SHIELDED R SERIES HIGH SPEED DIGITAL CABLE, 1M
156166-02	156166A-02 (rev A or higher)	SHIELDED R SERIES HIGH SPEED DIGITAL CABLE, 2M
156390-03	194210E-22L	USB 3 Cable, 3 Meter, A Jackscrews to Micro B Jackscrews
156391-03	156391A-03	USB 3 Cable, 3 Meter, A To MICRO B Jackscrews

Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxxX-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
156391-05	156391A-05	USB 3 Cable, 5 Meter, A To MICRO B Jackscrews
156789-02R4	156789B-2R4	2.4 M (8 FT) BNC Male-Mini-XLR Female Cable
156791-0R46	156791A-0R46	0.46 M (1.5 FT) MINI-XLR FEMALE-XLR FEMALE CABLE
156866-01	156866A-01	MINI DISPLAYPORT RETENTION ACCESSORY
157230-0R5	157230A-0R5	MINI DISPLAYPORT TO VGA ADAPTER, .5 M (0 TO 70 DEGREE CELSIUS)
157231-0R5	157231A-0R5	MINI DISPLAYPORT TO DVI ADAPTER, .5 M (0 TO 70 DEGREE CELSIUS)
157232-01	157232A-01	MINI DISPLAYPORT TO DISPLAYPORT CABLE, 1 M (-40 TO 85 DEGREE CELSIUS)
157232-02	157232A-02	MINI DISPLAYPORT TO DISPLAYPORT CABLE, 2 M (-40 TO 85 DEGREE CELSIUS)
157232-0R5	157232A-0R5	MINI DISPLAYPORT TO DISPLAYPORT CABLE, .5 M (-40 TO 85 DEGREE CELSIUS)
157253-01	157253A-01	PANEL MOUNTING KIT FOR 4-SLOT NI CRIO-9030/31/33/34 AND NI CDAQ-9132/34 SYSTEMS
157254-01	157254A-01	DIN RAIL MOUNTING KIT FOR 4-SLOT NI CRIO-9030/31/33/34 AND NI CDAQ-9132/34 SYSTEMS
157267-01	157267A-01	PANEL MOUNTING KIT FOR 8-SLOT NI CRIO-9035/36/38/39 AND NI CDAQ-9133/35 SYSTEMS
157268-01	157268A-01	DIN RAIL MOUNTING KIT FOR 8-SLOT NI CRIO-9035/36/38/39 AND NI CDAQ-9133/35 SYSTEMS
157350-01	152678A-01	SHIELDED CABLE FOR PXIE-4339 TO RACKMOUNT TERMINAL BLOCKS, 1 METER
157543-020	157543A-020	20 PIECE,STANDOFF,M/F,4.5 HEX,M3X7.15MM,SS,NP
157562-01	157562A-01	STANDOFF ACCESSORY FOR NI 9683
157570-01	157570A-01	POWER AND COMMUNICATION CABLE FOR AMULET DISPLAY
157788-01	157788A-01	USB CABLE WITH LOCKING SCREW FOR NI COMPACTRIO AND NI COMPACTDAQ CONTROLLERS, 1 M
158293-01	158293A-01	LEMO FEMALE TO PIGTAIL I/O CABLE, 1 M
158293-02	158293A-02	LEMO FEMALE TO PIGTAIL I/O CABLE, 2 M
158533-01	158533A-01	MODULE IMMOBILIZATION ACCESSORY FOR 8-SLOT COMPACTRIO AND COMPACTDAQ CONTROLLERS
158534-01	158534A-01	MODULE IMMOBILIZATION ACCESSORY FOR 4-SLOT COMPACTRIO AND COMPACTDAQ CONTROLLERS
180188-01	180188E-01	Bracket, GPIB, EMI Shield
180524-05	180524D-05	CABLE ASSY,50P,FLAT,NB1,.5M
181638-01	181638-01B	CONN,GPIB ADAPTER,TYPE XA
182009-02	182009D-02	CABLE ASSY,GPIB,TYPE X5,2M,STD GPIB TO SINGLE END MALE
182238-01	182238B-01 (Rev B or higher)	RS232 NULL-MODEM CABLE, DB-9 FEMALE TO DB-9 FEMALE, 1M
182419-02	182419C-02	Cable Assy, 2X68POS .050 Series D-Type, Shielded, Type SH6868,2M
182482-0R25	182482B-0R25	R6868 Low-Cost Unshielded Ribbon Cable, 0.25M
182671-01	182671E-01L	Conn Assy, SCXI-1349
182762-01	182762C-01	Cable Assy,100 Pos .050 Series D-Type to 2X50 Pos, Type R1005050,1M
182762-02	182762C-02	Cable Assy,100 Pos .050 Series D-Type to 2X50 Pos, Type R1005050,2M
182762-0R5	182762D-0R5	Cable Assy,100 Pos .050 Series D-Type to 2X50 Pos, Type R1005050, 0.5M
182766-01	182766A-01	Conn,Adapter,GPIB Bulkhead,F-F,Type XC
182770-01	182770A-01	CONN,ADAPTER,GPIB REVERSE ENTRY EXTENDER,M-F,TYPE XF
182845-01	182845C-01	Cable Assy,Serial,10 POS Modular Plug to 9 POS DSUB Plug,Type S8,1M
182849-01	182849C-01	CABLE ASSY,100 POS .050 SERIES D-TYPE TO 2 X 68POS,SHEILDDED,TYPE SH1006868,1M
182849-02	182849C-02	CABLE ASSY,100 POS .050 SERIES D-TYPE TO 2 X 68POS,SHEILDDED,TYPE SH1006868,2M
182849-05	182849D-05	CABLE ASSY,100 POS .050 SERIES D-TYPE TO 2 X 68POS,SHEILDDED,TYPE SH1006868,5M
182849-10	182849C-10	CABLE ASSY,100 POS .050 SERIES D-TYPE TO 2 X 68POS,SHEILDDED,TYPE SH1006868,10M
183045-01	183045C-01	RS232 STRAIGHT-THROUGH CABLE, DB-9 FEMALE TO DB-9 MALE,1M
183139-02	183139B-02	68F-50M DIO ADAPTER FOR 68-PIN DIGITAL BOARDS
183146-01	183146B-01	P4-BJ2 CABLE
183283-01	183283B-01	RS485 NULL-MODEM CABLE, DB-9 FEMALE TO DB-9 FEMALE, 1M
183285-01	183285C-01	X13 GPIB CABLE,MICRO D25 TO SHIELDED CABLE/STANDARD CONNECTOR,1M
183285-02	183285C-02	X13 GPIB CABLE,MICRO D25 TO SHIELDED CABLE/STANDARD CONNECTOR,2M
183432-01	183432C-01	Cable Assy, Type SH6868-D1,1M
183432-02	183432C-02	Cable Assy, Type SH6868-D1,2M

Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxxX-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
183432-05	183432C-05	Cable Assy, Type SH6868-D1,5M
184125-02	192256A-02	USB Cable, 2 Meter
184428-01	184428B-01	CABLE ASSY, SERIAL, 10 POS ISOLATED MODULAR PLUG TO 9 POS DSUB PLUG, 1METER
184483-01	184483B-01	Blank Connector Panel for CA-1000 Configurable Signal Conditioning Enclosure
184698-01	184698D-01	P2 PROBE SET
184721-01	184721B-01	Strain Relief Connector Panel for CA-1000 Signal Conditioning Enclosure
184736-01	184736B-01	Mini-Thermocouple Type J Connector Panel, CA-1000
184737-01	184737B-01	BNC Connector Panel, CA-1000 DAQ Accessory Enclosure
184738-01	184738B-01	9-PIN D-SUB Connector Panel for CA-1000 Configurable Signal Conditioning Enclosure
184738-02	184738B-02	Dual 9-PIN D-SUB Connector Panel for CA-1000 Configurable Signal Conditioning Enclosure
184738-03	184738B-03	9-PIN (Female), D-SUB Connector Panel for CA-1000
184738-04	184738B-04	Dual 9-PIN (Female), D-SUB Connector Panel for CA-1000
184748-01	184748B-01	CABLE ,SHC50-68, DIGITAL CABLE, 1M
184749-01	199006B-01	Cable, Type SH68-68-EP, Shielded Cable,1 Meter
184749-02	199006B-02	Cable, Type SH68-68-EP, Shielded Cable,2 Meter
184749-05	199006B-05	Cable, Type SH68-68-EP, Shielded Cable,5 Meter
184749-10	199006B-10	Cable, Type SH68-68-EP, Shielded Cable, 10 Meter
185095-01	185095D-01	Cable Assy, 2X 100-POS 0.050 Series D-Type, Shielded, FlexMotion, type SH100-100-Flex, 1M
185095-02	185095D-02	Cable Assy, 2X 100-POS 0.050 Series D-Type, Shielded, FlexMotion, type SH100-100-Flex, 2M
185262-01	185262C-01	CABLE ASSY, 2 X 68-POS .050 SERIES D-TYPE SHIELDED, TYPE SH68-68-S, 1 METER
185293-01	185293A-01	POWER SUPPLY,DESKTOP,100-240VAC IN,63HZ,IEC SOCKET,15VDC UNREGULATED OUT,1A,LOCKING PLUG, UK
185334-01	185334D-01	Panel Kit, TBX Cable Adapter for SCXI
185376-01	185376B-01	Four-LED Panelette Assembly, CA-1000 DAQ Accessory Enclosure
185378-01	185378B-01	Dual Toggle Switch Panelette Assembly, CA-1000 DAQ Accessory Enclosure
185444-01	185444B-01	CABLE, HV8-BAN4 (1 M)
185505-01	185505B-01	Panelette, SMB, Assembly, DAQ Accessory Enclosure (Pizza Box)
185692-01	185692C-01 (rev C or higher)	CABLE ASSY KIT, TYPE BAN-BARE, 1 METER
185797-02	185797A-02	Cable Assy,IEEE 1394,400MBPS,Non-Latching,2M
186380-02	186380C-02 (Rev C or higher)	KIT, CABLE ASSY, 2 X 68-POS VHDCI OFFSET, TYPE SHC68-C68-S, 2 METER
186380-0R5	186380-0R5	KIT, CABLE ASSY, 2 X 68-POS VHDCI OFFSET, TYPE SHC68-C68-S, 0.5 METER
186381-01	186381D-01	SH68-C68-S, 68 PON VHDCI TO 68 PIN 0.05 SERIES D-TYPE, 1 M
186405-01	186405B-01	Banana Jack Panel, CA-1000 DAQ Accessory Enclosure
186838-02	1192061C-02	SHC68-68-EP SHIELDED CABLE, 68-POSITION.050 SERIES D-TYPE TO 68-POS VHDCI OFFSET, 2 M
187106-01	187106A-01	Torque Wrench for SMA Connectors (1 NM) for Individual Sale
187243-01	187243B-01	Panel Mount Kit for SC-2345 OR CA-1000
187252-0R25	187252B-0R25 (rev B or higher)	RC68-68 RIBBON CABLE, 68 D-TYPE TO 68 VHDCI OFFSET, .25 M
187252-0R5	187252C-0R5	RC68-68 RIBBON CABLE, 68 D-TYPE TO 68 VHDCI OFFSET, .5 M
187322-02	187322C-01	RACK MOUNT FOR GPIB-ENET/100/1000, ENET-232/485, USB-232/485
187375-01	187375B-01	CABLE ASSY, ETHERNET, TYPE E, CROSSOVER, 8POS, CAT5, 1M
187375-05	187375B-05	CABLE ASSY, ETHERNET, TYPE E, CROSSOVER, 8POS, CAT5, 5M
187375-10	187375B-10	CABLE ASSY, ETHERNET, TYPE E CROSSOVER, 8POS, CAT5, 10M
187407-01	187407C-01	Strain Relief Kit For MID-76XX Series Motor Drive
187539-01	187539B-01 (rev B or higher)	M 2.5 SCREWLOCK FOR OEM
187591-01	187591B-01	Female 2-PIN MIL-C-26482 (Series 1), MS3112, Size 8
187597-03	187597B-03	Thermocouple (Type U) Connector Panel, CA-1000
187804-01	187804C-01	Cable Assy, IMAQ-DSHC68-04-1 Vision Products
187949-01	187949B-01	Accessory Hardware, Jacksocket Kit
187949-10	187949B-01	10 Piece Accessory Hardware, Jacksocket Kit
188143-01	188143D-01	SHC68-C68-D3 SHIELDED CABLE, 1 M
188399-01	188399B-01	CABLE ASSY, 4-PORT PCMCIA-232/485, 1 METER
188791-01	188791B-01	PCMCIA-CAN SYNCHRONIZATION CABLE, 1 M
188859-01	188859A-01	SMB 200 Cable, SMB Plug to SMB Plug Coax, 50 Ohm, 1M

Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxxX-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
189041-02	189041D-02	Cable Assy, 68-Position VHDCI Offset, Type SHC68-NT-S, Open Ended OEM, 2M
189174-01	189174A-01	Ethernet Cable Assy, Shielded, 8 Position, CAT 5, 1 M
189174-05	189174A-05	Ethernet Cable Assy, Shielded, 8 Position, CAT 5, 5 M
189174-10	189174A-10	Ethernet Cable Assy, Shielded, 8 Position, CAT 5, 10 M
189588-01	189588C-01	SHC68-68-RMIO CABLE, 68-POS .50 SERIES D-TYPE TO 68-POS VHDCI OFFSET, 1M
189588-02	189588C-02	SHC68-68-RMIO CABLE, 68-POS .50 SERIES D-TYPE TO 68-POS VHDCI OFFSET, 2M
189588-0R5	189588C-0R5	SHC68-68-RMIO Cable, 68-Pos .50 Series D-Type to 68-Pos VHDCI Offset, 0.5M OEM for Nanonis
190233-01	190233D-01	SHC68-C68-EPM SHIELDED CABLE, 68-POS VHDCI OFFSET TO 68-POS VHDCI OFFSET, 1M
190412-07	190412B-07	NI 5644R MIMO Flexible Cable Kit (Cables for RX & TX LOS) Qty 2
190654-01	190654B-01	Cable,10 POS Combicon -DB25M, 1 Meter
190654-02	190654B-02	Cable,10 POS Combicon -DB25M, 2 Meter
190656-01	190656B-01	Cable,10 POS Combicon -Pigtail, 1 Meter
190656-02	190656B-02	Cable,10 POS Combicon-Pigtail, 2 Meter
190846-01	190846B-01	RF CABLES (SMA TO SMB) FOR PXI-5670 PXI-5671, OR PXI-5610
190911-04	190911B-04	KIT, CABLE ASSEMBLY, DB25M-PIGTAIL, 4M
190912-04	190912B-04	KIT, CABLE ASSEMBLY, DB15M-PIGTAIL, 4M
190913-04	190913B-04	KIT, CABLE ASSEMBLY, DB9M-PIGTAIL, 4M
191006-01	191006A-01	CABLE ASSEMBLY, PCMCIA-CAN, SERIES 2, HS/HS
191667-01	191667A-01	SHC68-68-RDIO Cable, 68-Pos .50 Series D-Type to 68-Pos VHDCI Offset, 1M
191667-0R5	191667A-0R5	SHC68-68-RDIO Cable, 68-POS .50 Series D-Type to 68-POS VHDCI Offset, 0.5M OEM for NANONIS
191945-01	191945C-01	SHC68-68, TWISTED PAIR CABLE WITH BASIC SHIELDING, 1 M
191945-02	191945C-02	SHC68-68, TWISTED PAIR CABLE WITH BASIC SHIELDING, 2 M
192017-02	192017A-02	NI CAN SINGLE TERMINATION, HIGH-SPEED/FD CABLE, 2 M
192061-01	192061B-01	SHC68-68-EPM Shielded Cable, 68-Pos.050 Series D-Type to 68-Pos VHDCI Offset, 1M
192061-02	192061B-02	SHC68-68-EPM Shielded Cable, 68-Pos.050 Series D-Type to 68-Pos VHDCI Offset, 2M
192061-05	192061B-05	SHC68-68-EPM Shielded Cable, 68-Pos.050 Series D-Type to 68-Pos VHDCI Offset, 5M
192061-0R5	192061B-0R5	SHC68-68-EPM Shielded Cable, 68-Pos.050 Series D-Type to 68-Pos VHDCI Offset, 0.5M
192061-10	192061B-10	SHC68-68-EPM Shielded Cable, 68-Pos.050 Series D-Type to 68-Pos VHDCI Offset, 10M
192190-01	192190A-01	RJ50 10-PIN MODULAR PLUG TO DB-9 (MALE), 1 M
192288-0R3	192288B-0R3	SHC68-68M-EPM SHIELDED CABLE, MALE 68-POS .050 SERIES D-TYPE TO 68-POS VHDCI OFFSET, 0.3M
192344-01	192344A-01	SHB12X-B12X, SHIELDED CABLE, LVDS, 1 METER
192524-01	192524D-01	Expresscard Strain Relief Accessory for PXI Embedded Controllers
192568-01	192568A-01	SH25F-25M-1 25-PIN FEMALE TO MALE SHIELDED I/O CABLE, TWISTED PAIRS, HIGH CURRENT CAPACITY, 1 M
192568-02	192568A-02 (rev A or higher)	SH25F-25M-2 25-PIN FEMALE TO MALE SHIELDED I/O CABLE, TWISTED PAIRS, HIGH CURRENT CAPACITY, 2 M
192681-1R5	192681B-1R5	SHC68-H1X38 HIGH-SPEED DIGITAL FLYING-LEADS CABLE ACCESSORY, 1
192692-01	192692A-01	NI 9939 BACKSHELL FOR 16-POSITION CONNECTOR BLOCK (Qty 1)
193128-01	193128B-01 (rev B or higher)	NI CAN CABLE, NO TERM, HIGH-SPEED/LOW-SPEED, D-SUB 9-PIN F, 1M
193128-02	193128B-02 (rev B or higher)	NI CAN CABLE, NO TERM, HIGH-SPEED/LOW-SPEED, D-SUB 9-PIN F, 2M
193737-01	193737A-01	DB37M-DB37F-EP, 37-PIN SHIELDED CABLE FOR 4 ANALOG INPUTS, 4 ANALOG OUTPUTS AND 10 DIGITAL I/O BOARDS
193942-02	193942A-02	SAEJ1962M-DE9F CAN OBD-II Cable, SAE J1962 to D-SUB 9-POS F, No Termination
194096-01	194096A-01	IC Grabber Clips for High-Speed Digital Flying-Leads Cable, Set of 10
194123-01	194123A-01	MFIT-Pigtail Cable Assy, 14-Pin Digital I/O Cable for TB-2708/2709, 1M
194612-02	194612B-02	RJ50 Cable, 10-pin Modular Plug to 10-pin Modular Plug, 2M (Qty 4)
194612-10	194612B-10	RJ50 Cable, 10-PIN Modular Plug to 10-PIN Modular Plug, 10M
194738-01	194738B-01	NI 9944 QUARTER BRIDGE COMPLETION ACCESSORY (120 OHM, QTY 4)
194739-01	194739B-01	NI 9945 QUARTER BRIDGE COMPLETION ACCESSORY (350 OHM, QTY 4)
194881-01	194881B-01	NI 9957 Cartridge Die Cast Assembly (Qty 100)
195547-01	195547A-01	Extra Mounting Screws M4 X 17 (Qty 10)
195596-0R3	195596A-0R3	SHC68-Audio Cable Kit

Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxX-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
195712-01	195712A-01	NI WSN-3292, Replacement I/O Glands for WSN-3291. Includes 2 I/O Glands, 4 Gland Inserts & 2 Plugs
195738-01	195738A-01	NI WSN-3293, Replacement I/O Glands for WSN-3291. Includes 2 each of 5 Different Size Gland Inserts
195846-01	195846A-01L	653X Cable Adapter, 68-PIN D-Type to 68-PIN VHDCI Adapter with Screw Terminals for PFI Line Routing
195949-01	195949A-01	C68-68-D4 Unshielded Cable for High-Speed Digital I/O, 2x 68-Position VHDCI Offset, 1M
195950-02	195950A-02	RJ50 Cable, 10-pin Modular Plug to Pigtail Wires, 2M (Qty 4)
195950-10	195950A-10	RJ50 Cable, 10-pin Modular Plug to Pigtail Wires, 10M (Qty 4)
196236-1R5	196236A-1R5	SHB12X-H3X24 Differential Flying-Lead / Logic Analyzer Cable for High-Speed Digital I/O, 1.5 M
196275-01	196275A-01	SHC68-C68-D4 Shielded Single-Ended Cable for High-Speed Digital I/O, 1 M
196275-05	196275A-05	SHC68-C68-D4 Shielded Single-Ended Cable for High-Speed Digital I/O, 5 M
196283-04	196283A-04	Cable Assy IEEE 1394B to IEEE 1394B, 4 M
196284-04	196284A-04	Cable Assy IEEE 1394A to 1394B, 4 M
196304-30	196304A-30	Kit, GPS Antenna, Bullet III
196375-01	196375A-01	NI 9971 Backshell for 2-Position Connector Block (QTY 4)
196647-01	196647A-01	Cable Gland Replacement Pack, Elastomer, 4 Assorted Split and 2 Solid
196648-05	196648A-05	Cable M12, 2-PIN Female Connector to Pigtail, 5M
196649-05	196649A-05	Cable M12, 4-PIN Male Connector to Pigtail, 5M
196650-05	196650A-05	Ethernet Cable, Sealed Circular Plug to RJ45, 5M
196720-01	196720A-01 (rev A or higher)	NI 9972 BACKSHELL FOR 6-POSITION CONNECTOR BLOCK (QTY 4)
196741-01	762679-01	NI 9975 16-POSITION SCREW TERMINAL CONNECTOR BLOCK (QTY 2)
196809-01	196809B-01	NI 9949 RJ-50(FEMALE) TO SCREW TERMINAL ADAPTOR
196917-01	196917B-01L	NI 9977 C Series Filler Module for Empty Slot
196917-51	196917B-51L	NI 9977 C Series Filler Module for Empty Slot, RED MODULE (OEM)
197210-0R3	197210A-0R3	Mini-75 Ohm SMB Plug to Type F Female, 0.3M
197211-01	197211A-01	Mini-75 Ohm SMB Plug to Mini-75 Ohm SMB Plug, 1.0M
197211-0R3	197211-0R3	Mini-75 Ohm SMB Plug to Mini-75 Ohm SMB Plug, 0.3M
197516-01	197516A-01	4x Infiniband to 4x Infiniband Cable, 1M, For NI 449x and BNC-2144
197516-02	197516A-02	4x Infiniband to 4x Infiniband Cable, 2M, For NI 449x and BNC-2144
197545-01	197545A-01	Serial Cable - 68-POS VHDCI to DB-9M, 8-Port RS-232, 1M
197549-4R5	197549A-4R5	Cable Assy,1394B Jackscrew To Standard 1394B,Black,4.5 M
197817-05	197817A-05	NI 17XX 5M 15 Pin-M to 15 Pin-F Cable
197818-05	197818A-05	NI 17XX Pigtail Breakout Cable
197991-01	197991A-01	NI 9980 10-Position Spring Terminal
198141-2R5	198141A-2R5	D-Sub to D-Sub Cable For P70530 & P70360 Stepper Drives
198151-2R5	198151A-2R5	D-Sub to Leads Cable For P70530 & P70360 Stepper Drives
198159-01	198159A-01	PC-MF4-PT Power Cable C Series Microfit Female to Pigtail, .35M
198303-01	198303A-01	PC-MF4-Y Power Cable C Series Microfit Y-Adapter, Male to 2 Female, .2M
198506-01	198506D-01	USB Cable With Locking Screw, 1 M
198588-01	198588A-01	LVDS Flying Lead Extension Wires, Socket to Pin, 3.5 Inches, Set of 25
199006-01	199006B-01	Cable, Type SH68-68-EPM, Shielded Cable,1 Meter (Direct Replacement for SH68-68-EP)
199006-02	199006B-02	Cable, Type SH68-68-EPM, Shielded Cable,2 Meter (Direct Replacement for SH68-68-EP)
199006-05	199006B-05	Cable, Type SH68-68-EPM, Shielded Cable,5 Meter (Direct Replacement for SH68-68-EP)
199006-0R25	199006B-0R25	Cable, Type SH68-68-EPM, Shielded Cable,.25 Meter (Direct Replacement for SH68-68-EP)
199006-0R35	199006B-0R35	Cable, Type SH68-68-EPM, Shielded Cable,.35 Meter (Direct Replacement for SH68-68-EP)
199006-0R5	199006B-0R5	Cable, Type SH68-68-EPM, Shielded Cable,.5 Meter (Direct Replacement for SH68-68-EP)
199006-10	199006B-10	Cable, Type SH68-68-EPM, Shielded Cable, 10 Meter (Direct Replacement for SH68-68-EP)
199022-02	199022A-02	10P10C-DE9M-TS SERIAL CABLE, 10-POS PLUG TO DE9-M JACKSCREWS, 2M
199101-01	199101A-01	Jumpers, Red-Black Twisted Pairs, 3.5 Inches, 10 PCS
199198-01	199198C-01	NI PXI Slot Blocker, Set of 5
199254-01	199254A-01	SH37F-TAJIMI-1M Cable
199254-10	199254A-10	SH37F-TAJIMI-10M Cable
199429-01	199429A-01	Side Mounting Kit for NI PS-15
199430-01	199430A-01	Side Mounting Kit for NI PS-16

Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxxX-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
199431-01	199431A-01	Side Mounting Kit for NI PS-17
199432-01	199432A-01	Panel Mounting Kit for NI PS-15/16/17
199566-02	199566A-02	Cable Assembly, USB-8486 9 Pin Femal DSUB, 2M
199744-02	199744A-02	Cable, Power Over Camera Link(POCL), MDR to MDR, 2M
199744-05	199744A-05	Power Over Camera Link Cable (POCL), MDR to MDR, 5M
199745-05	199744A-05	Power Over Camera Link Cable (POCL), MDR to SDR, 5M
199746-05	199746A-05	Power Over Camera Link Cable (POCL), MDR to SDR, 5M
703071-01	703071A-01	FP Terminal Base GAL
745557-01	747038-01	Perforated DIN-Rail Mounting, 33cm
745557-02	747038-02	Perforated DIN-Rail Mounting, 50cm
745557-03	747038-03	Perforated DIN-Rail Mounting, 66cm
745687-K030	746067-01	K-TYPE THERMOCOUPLE WIRE(FIBERGLASS - 900 DEGREES F) 30 METER
763000-01	763864-01	POWER CORD,AC,U.S.,120VAC,2.3 METERS
763061-005	763507B- 0R5	CABLE ASSY,TYPE X2, 0.5M
763061-01	763507B-01	CABLE ASSY,TYPE X2,1M
763061-02	763507B-02	CABLE ASSY,TYPE X2,2M
763061-03	763507B-04	CABLE ASSY,TYPE X2,4M
763061-04	763507B-08	CABLE ASSY,TYPE X2,8M
763061-10	763507-10	CABLE ASSY,TYPE X2,10M
763064-01	763865-01	POWER CORD,240V,10A,U.K.
763065-01	763881-01	POWER CORD,220V,10A,SWISS
763067-01	763867-01	POWER CORD,240V,10A,EURO,RTANG
763072-01	763571-01	POWER CORD,250V,10A,INDIA
763389-01	199905A-0R61	SMB100 SMB PLUG TO BNC JACK,COAX,50 OHM,2FT
763427-05	763876-05	MXI-3 Fiber Optic Cable,5M
763427-301	763876-30	MXI-3 Fiber Optic Cable,30M
763431-05	763877-05	Cable Assy, MXI-3 Copper Cable, 5M
763431-10	763877-10	Cable Assy, MXI-3 Copper Cable, 10M
763431-30	763876-30	Cable Assy, MXI-3 Copper Cable, 30M
763443-01	763878-01	SMA Male Plug X SMA Male Plug (MAXI-FLEX) 5 Inches Long
763444-01	763879-01	SMA Male Plug X SMA Male Plug (MAXI-FLEX) 15 Inches Long
763507-02	763507B-02	Cable Assy, Type X2,2M
763634-01	769524-01	POWER CORD,AC,JAP,125VAC,15A
776249-02	180732E-02	RTSI BUS CABLES FOR 2 PCI OR AT/ISA DEVICES
776249-03	180732E-03	RTSI BUS CABLES FOR 3 PCI OR AT/ISA DEVICES
776249-04	180732E-04	RTSI BUS CABLES FOR 4 PCI OR AT/ISA DEVICES
776249-05	180732E-05	RTSI BUS CABLES FOR 5 PCI OR AT/ISA DEVICES
776572-80	181710F-01	SCXI-1180 (FEEDTHROUGH PANEL)
776572-81K	181385D-01 181385D-02 184799D-01 181596F-01	SCXI-1181K Module Components Kit
776576-60	181592G-01	SCXI-1360 (Front Filler Panel)
776576-61	181625D-01	SCXI-1361 (Rear Filler Panel)
776577-70	182598D-01 741223-01 741802-01 741510-01	SCXI-1370 Rack Mount Kit for SCXI-1001 AND PXI-1050
776577-74	182650B-01 (rev B or higher)	SCXI-1374 HANDLE KIT FOR PXI-1010
776582-01	712060-01	SCXI Process Current Res Kit
776784-05	182444-01 182323E-01	TYPE SH6850 68 TO 50 PIN SHIELDED CABLE,5M
776832-01	187539C-01	68-PIN MATING CONN/SHELL
776842-01	180524-10	R6850 68-50 PIN RIBBON CBL 1M
776990-01	182788E-01L	SCB-100 SHIELDED CONNECTOR BLK
777101-01	182943C-01L	CB-50LP CONNECTOR BLOCK W/O CABLE

Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxxX-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
777141-01	183420C-01L	TBX-68 CONNECTOR BLOCK
777163-01	182801A-001	MXI-2 TYPE M1,1M
777163-04	182801A-004	MXI-2 TYPE M1,4M
777163-08	182801A-008	MXI-2 TYPE M1,8M
777163-20	182801A-020	MXI-2 TYPE M1,20M
777164-01	182802A-001	MXI-2 TYPE M2,1M
777164-02	182802A-002	MXI-2 TYPE M2,2M
777164-04	182802A-004	MXI-2 Type M2, 4M
777164-06	182802A-006	MXI-2 TYPE M2,6M
777164-08	182802A-008	MXI-2 TYPE M2,8M
777164-20	182802A-020	MXI-2 TYPE M2,20M
777165-01	182803A-001	MXI-2 TYPE M3,1M
777165-02	182803A-002	MXI-2 TYPE M3,2M
777165-04	182803A-004	MXI-2 Type M3, 4M
777165-08	182803A-008	MXI-2 TYPE M3,8M
777165-20	182803A-020	MXI-2 TYPE M3,20M
777166-01	182804A-001	MXI-2 TYPE M4,1M
777166-02	182804A-002	MXI-2 TYPE M4,2M
777166-04	182804A-004	MXI-2 TYPE M4,4M
777180-01	711760-01	Quarter-Bridge Completion Resistor Pack, 120 OHM, 8 CT.
777180-02	711761-01	Quarter-Bridge Completion Resistor Pack, 350 OHM, 8 CT
777296-01	711835-01	FERRITE FOR RIBBON CABLES
777297-01	711627-01	EMI Suppression Ferrite 13.4 mm
777466-01	711856-01	Ferrite for IMAQ BNC Cable
777566-03	763860-01	RS232 Cable, 9Pin DSub, 3M
777600-01	187539C-01 760809-01 740238-01	68-POS Right Angle PWB Mounting
777601-01	187539C-01 740238-01 760811-01	68-Pin Vertical PWB Connector
777664-01	185097C-01 185257A-01	CA-1000 Enclosure Kit
777665-01	184887B-01	Rack-Mount Kit for SC-2345 OR CA-1000
777687-00	185161B-01L	SCXI-1300 LOW-VOLTAGE SCREW TERMINAL BLOCK, CAST
777687-02	185163B-01L	SCXI-1302 FEEDTHROUGH TERMINAL BLOCK,CAST
777687-10	185334D-01 760692-01 760694-01	SCXI-1310 96-Pin Connector and Shell Assy
777720-01	182444-01 185319B-01	CABLE ASSY KIT, SH5050 SHIELDED CABLE, 1 METER
777720-02	182444-01 185319B-02	CABLE ASSY KIT, SH5050 SHIELDED CABLE, 2 METER
777763-01	186012C-01	PXI-1000 Rack Mount 6U Front Panel Adapter, Converts 3U Modules for 6U Chassis
777779-01	761226-01 745444-01	100-PIN VERTICAL PWB CONNECTOR
777812-01	182762D-01 760405-01	CB-100 I/O KIT, DIN RAIL/PANEL/DESKTOP, 50-PIN CB'S, R1005050 CABLE, 1 M
777972-01	186889A-01	DIN RAIL/WALL MOUNTING KIT FOR UMI-FLEX-6 AND BNC BOXES
778134-01	761378-01 761375-01 761376-01 761377-01	MID Spare Connector Kit
778242-01	187310B-01L	TB-2715, PXI Terminal Block for Digital I/O
778353-01	765462-01	SMA 50 OHM Termination Plug
778354-01	761635-01	SMB 50 OHM Termination Plug
778414-01	763405-01	SMB110, SMB FEMALE TO BNC MALE COAX CABLE,1M, QUANTITY 8

Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxX-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
778415-01	199905A-0R61	SMB100 SMB FEMALE TO BNC FEMALE COAX CABLE,50 OHM,2 FT, QUANTITY 8
778556-01	188457G-02L (rev G or higher)	UMI-7772 2 AXIS UNIVERAL MOTION INTERFACE, DSUB CONNECTORS
778558-01	188457G-01L (rev G or higher)	UMI-7774 4 AXIS UNIVERAL MOTION INTERFACE, DSUB CONNECTORS
778616-01	189048B-01	CFP-PM-H COMPACT FIELDPOINT PANEL MOUNT KIT, HORIZONTAL
778620-04	188843B-01	SH37F-P-4 37-PIN FEMALE TO PIGTAILS SHIELDED I/O
778621-01	188841B-01	SH37F-37M-1 37-PIN FEMALE TO MALE SHIELDED I/O CABLE, 1 M
778622-1024	695463-1024	1GB CompactFlash Industrial Non-Volatile Storage Memory
778622-2048	695463-2048	2GB CompactFlash Industrial Non-Volatile Storage Memory
778622-4096	695463-4096	4GB CompactFlash Industrial Non-Volatile Storage Memory
778622-512	695463-512	512 MB COMPACTFLASH INDUSTRIAL NONVOLATILE STORAGE MEMORY
778622-64	695463-064	64 MB COMPACTFLASH INDUSTRIAL NONVOLATILE STORAGE MEMORY
778643-01	189361B-01	NI PXI 8-SLOT FRONT RACK MOUNT KIT
778643-02	189362B-01	Kit, Rack Mount, Rear, PXI Chassis, 8-Slot
778644-01	190274B-01	NI 14/18-SLOT CHASSIS FRONT RACK MOUNT KIT
778644-02	190303B-01	NI 14/18-SLOT CHASSIS REAR RACK MOUNT KIT
778646-01	189864B-01	PXI Filler Panel Kit for 18 Slot Chassis
778679-01	189328B-01	PXI Chassis Filler Panel Kit
778688-01	189085B-01	CFP-PM-V COMPACT FIELDPOINT PANEL MOUNT KIT, VERTICAL
778709-01	189085B-01	UMI-7774, Panel Mount, Vertical
778710-01	188742B-01	DIN Rail Mount for UMI-7772/4
778711-01	189084B-01	Panel Mount Horizontal for UMI-7772/4
778712-01	189331B-01	UMI-7774, Rack Mount
778713-02	763608-01	USB to Dual PS2 Keyboard/Mouse Adapter Cable
778796-01	196978A-4R5	Cable Assy, 1394 Jackscrews to Standard 1394 , 4.5M
778827-01	150205A-01	SMB112, DOUBLE SHIELDED SMB BNC MALE COAX CABLE, 50 OHM, 1M
778831-01	761930-01	MCX 50 OHM Termination Plug
778914-01	765368-01	Connector, .8MM Champ, 68 POS, VHDCI, Through Hole
778931-02	190945B-01	Rear Rack Mount Kit for PXI-1052
778933-01	190961B-01	PXI Filler Panel Kit for 4 & 6-Slot Chassis
778948-01	191122B-01	PXI-103X and PXIE-107X Rack Mount Kit
778949-01	191124A-01	PXI-103X Side Handle and Rubber Feet Kit
778959-10	763561-10	MXI-4 Fiber Optic Cable, 10 M
778959-200	763561-200	MXI-4 Fiber Optic Cable, 200 M
778959-30	763561-30	MXI-4 Fiber Optic Cable, 30 M
778962-01	762120-01	Extra Cable Connectors for NI TB-2630
779016-01	779016A-01	NI 9935 15 Pin D-Sub Connector Kit
779017-01	779017B-01	NI 9932 BACKSHELL WITH 10-POSITION CONNECTOR BLOCK (QTY 1)
779018-01	194672B-01	NI 9915 DIN Rail Mounting Kit For 8-Slot Chassis
779019-01	194673C-01	NI 9912 DIN Rail Mounting Kit for 4-Slot COMPACTRIO Chassis
779020-03	189964B-01	CRIO-9951 Input/Output Communication and Control (IOCC) Module Development Kit for COMPACTRIO
779038-02	192004C-01	LFH200 TO 4X50-PIN DSUB SWITCH CABLE (CH-COM TWISTED), 1M
779038-03	192003B-01	LFH200 TO 4X50-PIN DSUB SWITCH CABLE (CH-CH TWISTED), 1M
779097-01	194032C-01	NI 9904 Horizontal Panel Mounting Kit For 4-Slot Chassis
779102-01	194019A-01	NI 9910 Industrial Sliding Rack-Mount Kit For 4 or 8 Slot Compact RIO & Compact DAQ chassis
779104-01	762284-01 762282-01 762283-01	NI 9934 25 PIN D-SUB Connector Kit
779105-01	761980-01	NI 9936 10-Position Screw Terminal Connector Block (Qty 10)
779106-01	761879-01	NI 9937 4-POS Controller Power Supply Plugs (Qty 10)
779133-01	189964A-01	CRIO-9952 Module Shell, 10-POS Screw Terminal Slot, No LED Slot, w/PCB Connectors (Qty 10)
779134-01	189964B-01 191305A-01	CRIO-9953 MODULE SHELL, NO CUT OUTS, W/PCB DSUB CONNECTOR TO CRIO CHASSIS (QUANT 10)
779157-01	746404-01	Connector, LVDS, Right Angle

Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxxX-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
779175-02	770090-01	40GB (Or Greater) 2.5 IN PATA Ext Temp Blank HDD Spare/Replacement
779175-03	770097-060	60 GB (OR GREATER) 2.5 IN SATA BLANK HDD SPARE/REPLACEMENT
779175-04	770097-120	120 GB (Or Greater) 2.5 IN SATA Blank HDD Spare/Replacement
779175-06	770097-250	250 GB (Or Greater) 2.5 IN SATA Blank HDD Spare/Replacement
779175-07	770095-080	80 GB (Or Greater) 2.5 IN SATA Extended Temp, 24/7 Hard Drive Upgrade
779175-08	747125-01	32 GB 2.5 IN SATA Solid State Hard Drive Upgrade
779183-01	192387C-01L	TB-2706, PXI FRONT-MOUNT SCREW TERMINAL BLOCK FOR M SERIES DAQ
779184-01	762285-01	TB-37F-37SC 37-Pin Solder Cup Terminals, Shell W/Strain Relief
779198-01	762409-01	CB-15 15-PIN Screw Terminal Connector Block, DIN-Rail Mountable
779200-01	192026B-01	PXI-1044 Filler Panel Kit, 7 Single, 1 Double, 1 Quadruple, W/Instructions
779302-1024	693851-1024 695526-1024	1 GB DDR2 RAM for NI 8106, NI 8105, and NI 8104 Controllers
779302-512	693851-512 695526-512	512 MB DDR2 RAM for NI 8106, NI 8105, and NI 8104 Controllers
779323-01	192533B-01L	SMA-2164 LVDS PROTOTYPING ACCESSORY
779325-01	763592-01	16-PIN Row Expansion Cable for TB-264X
779346-01	763612-01 763611-01	Row & Column Cable Kit for NI TB-264X Terminal Blocks (1.5 M)
779352-01	180524E-01	Camera Link I/O Extension Board (PCI)
779356-01	192916A-01	Relay Replacement Kit for IM42GR Relays (QTY: 10)
779371-01	191813C-01 762242-01	NI USB-6008/6009 Accessories: 4 Connectors, 2 Labels, 1 Screwdriver
779376-01	192345A-01 762242-01	NI USB-6501 Accessories: 4 Connectors, 2 Labels, 1 Screwdriver
779442-01	762189-01	6 Screw-Terminal Connectors for DAQPAD-6016 OEM Version
779473-01	192516C-01	NI 9901 DESKTOP MOUNTING KIT
779499-01	193138A-01	Low-Leakage, Low-Thermal Connectivity Cable Kit
779500-01	193355A-01	MXI-Express/Expresscard MXI Cable, 1M
779500-03	193355A-03	MXI-Express/ExpressCard MXI Cable, 3M
779500-07	193355A-07	MXI-Express/ExpressCard MXI Cable, 7M
779554-01	192941C-01L	TB-2709, PXI FRONT-MOUNT SMB TERMINAL BLOCK FOR PXI-6123 AND PXI-6133 S SERIES DAQ
779567-01	746496-01	NI 9940 Strain-relief & High-voltage Connector kit for 36-Position Connector
779568-01	194589A-01	NI 9941 Strain-relief & High-voltage Connector kit for 36-Position Connector (Use Only with NI 9206)
779570-01	762745-01 762744-01 762743-01	NI 9943 9-PIN Connector Kit With Strain Relief
779571-01	765479-01	NI 9946 4-POS NI 9505 Plugs (Qty 10)
779581-01	762710-01	4x2 Header Receptacles for Digital Flying-Leads Cable, Set of 10
779611-01	185095D-02 (rev D or higher) 193615C-01L (rev C or higher)	MCA-7790Y, MOTION INTERFACE AND CABLE FOR CONNECTIVITY TO YASKAWA SERVO DRIVES
779612-01	185095D-02 193609B-01L	MCA-7790M, MOTION INTERFACE AND CABLE FOR CONNECTIVITY TO MITSUBISHI SERVO DRIVES
779613-01	185095D-02 193612B-01L	MCA-7790P, Motion Interface and Cable for Connectivity to Panasonic Servo Drives
779674-01	762906-01	SMA Plug (Female) to SMB Jack (Male) Adapter
779689-01	740872-01	DIN Rail Mounting Kit for DAQ and GPIB Devices
779697-02	183882-02	BNC Male (PLUG) To BNC Male (PLUG) Cables, 2M, 4 Pack
779701-03	193355A-03 194402G-01L 196115A-01 199042B-01L	NI PXIE-PCIE8361, X1 MXI-EXPRESS FOR PXI EXPRESS, 1 PORT PCIE, 3 M CABLE
779725-03	195994A-03	X4 MXI-EXPRESS CABLE, 3 M
779725-07	195994A-07	X4 MXI-EXPRESS CABLE, 7 M
779727-01	760814-01	PSC-760 Power Connector for Alternate Power Supply

Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxxX-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
779729-01	762478-01	cFP-180x Power Supply Connector For Compact Fieldpoint
779783-01	196418A-01	176-Pin Right Angle Female Connector for XX30 Switch Modules
779806-01	195968B-01 195967A-01 195969A-01 762242-01	NI USB-621X Accessories: 4 Connectors, 1 Label, 1 Screwdriver
779807-01	195968B-01 195967A-01 195969A-01 761862-01	NI USB-621X Premium Accessories: 4 Connectors w/ Screw Flanges, 1 Label, 1 Screwdriver
779915-1024	695279-1024	1 GB DDR2 RAM for NI PXIe-8103 Controller
779937-01	194417B-01 762242-01	NI USB-6525 Accessories: 4 Connectors, 2 Labels, 1 Screwdriver
779956-01	194017A-01	62-Pin Female-to-Female Shielded DSUB Cable for NI PXI-2568
779980-01	746786-01	CAMERA, BASLER SCA1390-17FM, IEEE 1394B, 1392X1040, 17 FPS
779981-01	746787-01	CAMERA, BASLER SCA1390-17GM, GIGE, 1392X1040, 17 FPS
779982-01	746788-01	CAMERA, BASLER SCA640-70FM, IEEE 1394B, 659X490, 70 FPS
779983-01	746789-01	CAMERA, BASLER SCA640-70GM, GIGE, 659X490, 70 FPS
779984-01	763799-01	Basler I/O Cable for IEEE 1394B Cameras
779985-01	763799-01 763800-01	Basler I/O Cable for GIGE Cameras
779986-01	723244-01	Basler Power Supply for GIGE Vision Cameras
780024-01	746815-01	Lens, 8MM, Megapixel, Computar
780025-01	746818-01	Lens, 12MM, Megapixel, Computar
780026-01	746819-01	Lens, 16MM, Megapixel, Computar
780027-01	746820-01	Lens, 25MM, Megapixel, Computar
780031-2048	694972-2048	2 GB DDR2 RAM FOR NI VXIPC-882 CONTROLLERS
780041-01	197864B-01L	NI CAN Breakout Box 7-Port for CAN, Devicenet, Canopen
780151-01	765381-01	Spare Power and Motor Connectors for P7000 Stepper Drives
780216-01	780216A-01	NI 9965 Backshell for 24-Pos Spring Terminal
780221-01	746987-01	4x4 Back Light (Red), BL0404, Advanced Illumination
780222-01	746986-01	Ring Light (Red), RL1424, Advanced Illumination
780223-01	746989-01	Linear Array (Red), LL5806, Advanced Illumination
780224-01	746988-01	Spot Light (Red), SL2420, Advanced Illumination
780246-01	746662-01	2 GB SD Card, Industrial Rated for NI 9802
780251-01 780252-01	198917B-01	ENCODER, 15T-01SA-1000-N5RHV-F00-CE, MOTOR MOUNT, 0.25" THRU BORE, 1000CPR, 5V LINE DRIVER OUTPUT
780259-01	761785-01	CVS-145X Power Supply Connector
780284-01	763983-01	NI SP200B 10:1 AND 1:1 SWITCHABLE PASSIVE OSCILLOSCOPE PROBE, 60 V
780315-01	747070-01	Rugged Carrying Case for Portable Instrumentation
780327-03	195994A-03	VXI-MXI-Express Trigger Cable, 3M
780327-07	195994A-07	VXI-MXI-Express Trigger Cable, 7M
780389-01	763083-01	VHDCI Connector, 68-pin, Vertical, PWB Through Hole Mount
780390-01	762496-01	VHDCI Connector, Dual Stack, 68-pin, Right Angle, PWB Through Hole Mount
780398-01	747070-01	PXI & PXIe Carrying Case for 4, 6, or 8-Slot chassis and/or NI PMA-1115
780446-2048	695289-2048	2 GB DDR2 RAM for NI 8108 Controller
780446-4096	695289-4096	4 GB DDR2 RAM for PXI-8108 & PXI-8110 Controller
780487-01	747141-01	Torque Screwdriver (100 NCM)
780534-01	198506C-02	Cable Assy, Locking USB, 2M
780540-01	765551-01	Ref Clk T Connector, SMA Female/Male/Female, 50Ohm
780553-01	765530-01 198507A-01	NI 951X Cable and Terminal Block Bundle
780557-01	762898-01 762897-01 762916-01 762915-01	Combicon Connector Kit: 6-Pos, 2-Pos, Backshells

Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxxX-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
780566-02	190412B-04 190434A-01	PXIe-5663/5663E MIMO Cable Kit
780567-02	190412B-04 190435A-02	PXIe-5673/5673E MIMO Cable Kit
780571-01	190411A-01	NI 9931 Motor Screw Terminal Accessory for NI 9505
780576-01	198506C-02	Cable Assy, Locking USB, 2M, QTY 5
780679-01	189587C-01 190703A-01	NI 9908 DIN Rail Mounting Kit for Stand Alone CRIO-9014 (REV G or Later) Controller
780702-01	765252-01	2-Position Screw Terminal Kit for Power Supply Connection, Quantity 4
780703-01	190415A-01 (rev A or higher)	NI PS-9 DESKTOP POWER SUPPLY, 12 VDC, 1.25 A, 100-240
780711-01	198876A-02 193944A-01	NI FLEXRIO Adapter Module Development Kit
780716-01	190739A-01 190703A-01	NI 9909 Panel Mounting Kit for Stand Alone CRIO-9014 (REV G or Later) Controller
780868-01	763801-01	DVI-I (Male) TO DVI-D (Female) & VGA (Female) Splitter
780889-01	198998A-01	176-Pin Cable for the PXI-2530
780892-01	193944A-01	NI FLEXRIO Windowed Adapter Module Enclosure (Qty 1)
780892-10	193944A-01	NI FLEXRIO Windowed Adapter Module Enclosure (Qty 10)
780893-01	198876A-02	NI FLEXRIO Blank Adapter Module Enclosure (Qty 1)
780893-10	198876A-02	NI FLEXRIO Blank Adapter Module Enclosure (Qty 10)
780893-25	195549A-01 198876A-03	NI FLEXRIO Blank, Unpainted Adapter Module Enclosure
780895-01	190487A-01	RF Torque Screwdriver and SMA Driver Bit
780910-01	746984-01	Fan Replacement Kit for PXI-103X Chassis
780954-01	196842A-01	NI 9902 Desktop Mounting Kit
780965-01	195391A-01	NI sbRIO-9691 Module Stack Kit for sbRIO-960X
780966-01	196470A-01	NI sbRIO-9692 Module Stack Kit for sbRIO-961X/3X/4X
780982-01	190962B-03	NI 9916 DIN RAIL KIT FOR 14-SLOT MXI-EXPRESS RIO CHASSIS AND CDAQ-9179
780999-01	194972A-01	WSN 3280, WSN Node Panel Mount Kit with Node Locking Mechanism and Strain Relief for Wiring
781013-01	196275A-0R55	SHC68-C68-D4 Shielded Single-Ended Cable for High Speed Digital I/O Instruments, 0.5 Meter
781017-03	762432-01 762183-01 761980-01 761979-01 760873-01 746037-01 740981-01 191721A-00 191720A-00 190122A-00 189964B-01 762432-01 762183-01 761980-01 761979-01 760873-01 746037-01 740981-01 191721A-00 191720A-00 190122A-00 189964B-01	CRIO-9951 Module Development Kit Base - Limited Use License
781070-01	747293-01	SPARE 250 GB HARD-DRIVE FOR NI 8260
781073-01	199297A-01	NI WSN-3281, WSN Node Magnetic Panel Mount Kit w/ Node Locking Mechanism and Strain Relief for Wiring

Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxxX-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
781074-01	199326A-01	NI WSN-3282: WSN DIN Rail Mounting Kit for Measurement Nodes or Ethernet Gateway
781075-01	199337A-01	NI WSN-3283, WSN Panel Mount Plate for Nodes or Ethernet Gateway
781076-01	765593-01 765464-01	NI WSN-3284, Extra 18-Position Screw Terminal Connectors for NI WSN-3202 - 2 Top Entry, 2 Side Entry
781077-01	765593-01 765464-01	NI WSN-3285, Extra 18-Position Screw Terminal Connectors for NI WSN-3212 - 2 Top Entry, 2 Side Entry
781081-01	765630-01	25-PIN DSUB to Screw Terminal Block, DIN Rail Mount
781150-01	747438-01	EXPRESSCARD TO GIGABIT ETHERNET ADAPTER (WINDOWS ONLY)
781153-01	743148-01	PXI 18-Slot Front Panel Protector
781175-01	199968A-01	Combicon Connector Kit (8-POS 5.08MM, Backshell)
781202-01	763967-01	2M DVI-I TO DVI-I Monitor Cable For NI FPM-1019 Monitor
781233-02	711849-01	EMI Suppression Ferrite 10.2 mm
781255-01	747752-01	Greenfield PXI-9404 Precision Delay Generator
781266-01	151855A-12	50-OHM, MMCX TO SMB, Coaxial Cable
781293-01	196275A-02	SHC68-C68-D4 Shielded Single-Ended Cable for High SED Digital I/O Instruments, 2 Meter
781362-01	199373B-0R55	SHC68-C68-D5 Cable for NI 2515 HSDIO Signal Insertion 0.5M
781364-01	151749A-01	NI PXIe-1078 Rack Mount Kit
781384-01	747388-01	Quanser QNET MYOELECTRIC Board for NI ELVIS
781414-01	747336-01	LENS,8.5MM,COMPACT FIXED FOCAL LENGTH, EDMUND OPTICS
781415-01	747337-01	LENS,12MM,COMPACT FIXED FOCAL LENGTH, EDMUND OPTICS
781416-01	747338-01	LENS,16MM,COMPACT FIXED FOCAL LENGTH, EDMUND OPTICS
781417-01	747339-01	LENS,25MM,COMPACT FIXED FOCAL LENGTH, EDMUND OPTICS
781418-01	747340-01	LENS,35MM,COMPACT FIXED FOCAL LENGTH, EDMUND OPTICS
781436-01	150796A-01	Industrial Sliding Rack Mounting Kit, 14-Slot cRIO and cDAQ CHASSIS
781468-01	747702-01	Battery Backup Module For HDD-8265
781503-01	150888A-01L	NI 9923 Front-Mount Terminal Block for 37-PIN D-SUB Modules
781508-2048	696297-2048	2 GB DDR3 RAM for PXI-8109 Controller
781508-4096	696297-4096	4 GB DDR3 RAM for PXI-8109 Controller
781514-01	150971A-01 150972A-01	USB X SERIES MOUNTING KIT
781515-01	150971A-01 150972A-01 194905A-01	USB X SERIES MOUNTING KIT WITH DIN RAIL CLIP
781516-01	199588A-02L	SMB-2145 16-Channel Output Digital I/O Accessory
781517-01	189408E-04L	SMB-2146 2 Channel Input, 16 Channel Output Digital I/O Accessory
781518-01	189408E-05L	SMB-2147 16 Channel Analog Input Accessory
781519-01	189408E-06L	SMB-2148 8 Channel Input, 8 Channel Output Digital I/O Accessory
781526-01	150640A-2R5 (rev A or higher) 747215-01	UMI-7772/74 TO AKD DRIVE CABLE
781600-01	764115-01	PRECISION ADAPTER, N-TYPE, MALE-MALE
781602-01	764117-01	PRECISION ADAPTER, N-TYPE, MALE-FEMALE
781603-01	764118-01	PRECISION ADAPTER, N-TYPE MALE TO K-TYPE MALE
781623-01	747687-01	PXI-1071 CHASSIS FAN REPLACEMENT KIT
781682-01	198098A-06L	NI 1732 SMART CAMERA(400 MHZ PROCESSOR, VGA, MONOCHROME)
781683-01	198098A-07L (rev A or higher)	NI 1752 SMART CAMERA (600 MHZ PROCESSOR, VGA, MONOCHROME)
781684-01	198098A-08L (rev A or higher)	NI 1754 SMART CAMERA (600 MHZ PROCESSOR, SXGA, MONOCHROME)
781687-01	151831A-01L	NI TB-2630B, Terminal Block for NI PXI-2530B as Multiplexer
781692-01	151999A-01	LFH160 TO 50-PIN D-SUB FOR NI PXI-2530B
781722-01	152004A-01	NI 9903 Horizontal Panel Mounting Kit for 9181/91 Chassis
781723-01	151092A-01 152110A-01	NI 9925, OUTDOOR ENCLOSURE FOR NI CDAQ-9181/91
781740-01	188742B-04	NI 9913 DIN Rail Kit for NI 9181/9191 Chassis
781763-01	769032-01	X16 MXI-Express Cable, 1M
781763-03	763134-03	X16 MXI-Express Cable, 3M

Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxxX-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
781769-01	747907-01	SEIKO GIKEN HANDI MATE 2.5MM AND 1.25MM CLEANER, OVER 500 SWIPES
781785-01	152499A-01	NI 5191 800 MHZ Differential Active Probe
781822-01	152541A-01L	NI 9930Y, Motion Control Accessory, NI 9512 to Yaskawa Servo Drives
781823-01	152454A-01L	NI 9930P, Motion Control Accessory, NI 9512 to Panasonic Servo Drives
781824-01	152457A-01L	NI 9930M, Motion Control Accessory, NI 9512 to Mitsubishi Servo Drives
781845-01	151957A-01	Cable Assy, SMA to SMA, Coax, RG-402, 50 OHM, 1 Meter
781846-01	151957A-0R3	Cable Assy, SMA to SMA, Coax, RG-402, 50 OHM, 0.3 Meters
781864-1024	696333-1024	1 GB DDR2 RAM for PXIe-8100 Controller
781864-512	696333-512	512 MB DDR2 RAM for PXIe-8100 Controller
781877-01	748033-01	Camera, Basler, ACA750-30GM, GIGE, 752X580, 30FPS, Monochrome
781878-01	748034-01	Camera, Basler, ACA750-30GC, GIGE, 752X580, 30FPS, Color
781895-01	152488A-0R5	SHC68-C68 RMIO and RDIO Cables for Optimedia, 68-PIN VHDCI to 68-PIN VHDCI, 0.5 M
781913-01	748153-01	VERT 2450: 2.4 and 5 GHZ Dual Band Vertical Antenna
781915-01	748154-01	VERT 400: 144 MHZ, 400 MHZ, 1200 MHZ, TRI Band Vertical Antenna
781916-01	763294-01	NI USRP-292X MIMO Sync and Data Transfer Cable, 0.5M
781918-01	151611A-01 151612A-01 190412B-05	NI PXIe-5665 3.6 GHZ VSA Cable Kit
781919-01	152886A-01	NI Panel Mount Kit for CRIO-908X
781922-01	151628A-01L	NI 9924 Front-Mount Terminal Block for 25-PIN D-SUB Modules
781945-01	747474-480	300GB OR GREATER 2.5 IN MLC SATA EXT TEMP 24/7 SSD UPGRADE
781946-01	747979-500	500 GB 2.5 IN SATA Hard Drive Upgrade
781950-01	611335-01	EMI Suppression, Ferrite, Round Cable
781965-01	748090-01	AKM11F-ANMN2-00 BLDC Motor, 4057 RPM@24VDC, 0.128NM
781965-02	748091-01	AKM11E-ANMN2-00 BLDC Motor, 2002 RPM@24VDC, 0.180NM
781965-03	748092-01	AKM21I-ANMN2-02 BLDC Motor, 3270 RPM@24VDC, 0.197NM
781965-04	748093-01	AKM21G-ANMN2-00 BLDC Motor, 1958 RPM@24VDC, 0.289NM
781965-05	748094-01	AKM21F-ANMN2-00 BLDC Motor, 1300 RPM@24VDC, 0.354NM
781965-06	748095-01	AKM21E-ANMN2-00 BLDC Motor, 721 RPM@24VDC, 0.447NM
781970-01	748089-01	AKM24F-BNBNC-00 BLDC Motor with SFD, 3000RPM@160VDC, 4.82NM
781974-01	152514A-01(Rev A or higher) 762284-01	NI PXIe-4140/4141 Connector Kit
781987-01	152825A-01(Rev A or higher)	DIN Rail Mounting Kit for COMPACTRIO 908X Systems
781988-01	152829A-01(Rev A or higher)	Desktop Mounting Kit for COMPACTRIO 908X Systems
781989-01	153018A-01(Rev A or higher)	Rack Mount Kit for cRIO Ssystems
781993-01	152919A-03(Rev A or higher) 152920A-01(Rev A or higher) 765252-01	Power & I/O Accessory for NI 177X Smart Cameras
782033-01	748164-01	Single Axis AKD Drive, ECAT, 6A Continuous Current, 240/480VAC, 3 Phase
782034-01	748165-01	AKM72P-ANCNC-00 BLDC Motor with SFD, 2170PM@320VDC, 29.4NM
782060-01	151611A-01(Rev A or higher) 151612A-01(Rev A or higher) 763282-07	NI PXIe-5665 14 GHZ VSA Cable Kit
782084-01	748192-01	AKM24D-ASB2C-02 BLDC Motor, 3/8" Shaft and 1" Shaft Length
782086-01	748195-01	AKM44H-ANC2C-00 BLDC Motor with SFD, 1630RPM@160VDC, 5.89NM
782098-01	748210-01	AKM31E-NACNC-00 BLDC Gear Motor with SFD, 90MM Frame, 10:1 Reduction Ratio
782106-01	152361A-01(Rev A or higher)	Replacement Power Supply for NI PXIe-1066DC
782107-01	152665A-01(Rev A or higher)	Replacement Fan Assembly for NI PXIe-1066DC
782116-01	748532-01	SPARE OPTICAL DRIVE FOR NI RMC-8355
782130-001	763318-01	Motor Power Cable w/Brake, AKM Motor to AKD Drive, 1M
782130-03	763372-03	Motor Power Cable w/Brake, AKM Motor to AKD Drive, 3M
782131-01	152846A-01(Rev A or higher)	cRIO Profinet Sslave C Series Module
782138-01	748230-01	BASLER ACE CAMERA, ACA640-90GM, 659 X 494, 90 FPS, MONOCHROME
782139-01	748231-01	BASLER ACE CAMERA, ACA640-90GC, 659 X 494, 90 FPS, COLOR
782140-01	748232-01	BASLER ACE CAMERA, ACA1600-20GM, 1628 X 1236, 20 FPS, MONOCHROME
782141-01	748233-01	BASLER ACE CAMERA, ACA1600-20GC, 1628 X 1236, 20 FPS, COLOR

Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxxX-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
782150-01	748238-01	BASLER SCOUT CAMERA, SCA640-74FC, 658 X 492, 74 FPS, COLOR
782151-01	748239-01	BASLER SCOUT CAMERA, SCA640-120FM, 659 X 493, 120 FPS, MONOCHROME
782152-01	748240-01	BASLER SCOUT CAMERA, SCA640-120FC, 659 X 493, 120 FPS, COLOR
782153-01	748241-01	BASLER SCOUT CAMERA, SCA750-60FM, 752 X 480, 64 FPS, MONOCHROME
782154-01	748242-01	BASLER SCOUT CAMERA, SCA750-60FC, 752 X 480, 64 FPS, COLOR
782155-01	748243-01	BASLER SCOUT CAMERA, SCA780-54FM, 782 X 582, 58 FPS, MONOCHROME
782157-01	748244-01	BASLER SCOUT CAMERA, SCA1000-30FM, 1034 X 779, 30 FPS, MONOCHROME
782158-01	748245-01	BASLER SCOUT CAMERA, SCA1000-30FC, 1034 X 779, 30 FPS, COLOR
782160-01	748246-01	BASLER SCOUT CAMERA, SCA1300-32FC, 1296 X 966, 33 FPS, COLOR
782164-01	748247-01	BASLER SCOUT CAMERA, SCA1400-17FM, 1392 X 1040, 17 FPS, MONOCHR
782165-01	748249-01	BASLER SCOUT CAMERA, SCA1400-17FC, 1392 X 1040, 17 FPS, COLOR
782166-01	748250-01	BASLER SCOUT CAMERA, SCA1400-30FM, 1392 X 1040, 30 FPS, MONOCHROME
782167-01	748251-01	BASLER SCOUT CAMERA, SCA1400-30FC, 1392 X 1040, 30 FPS, COLOR
782170-01	748252-01	BASLER SCOUT CAMERA, SCA1600-14FC, 1628 X 1236, 14 FPS, COLOR
782171-01	748253-01	BASLER SCOUT CAMERA, SCA1600-28FM, 1628 X 1236, 28 FPS, MONOCHROME
782172-01	748254-01	BASLER SCOUT CAMERA, SCA1600-28FC, 1628 X 1236, 28 FPS, COLOR
782175-01	748255-01	BASLER SCOUT CAMERA, SCA640-74GM, 658 X 492, 79 FPS, MONOCHROME
782271-01	153182A-01	DISPLAY PORT TO VGA ADAPTER CABLE
782337-06	763343-06	Flex Motor Power Cable w/Brake, AKM Motor to AKD Drive, 6M
782337-10	749249-01	CP-507CDAN-10-0, MOTOR POWER CABLE, AKM MOTOR TO AKD DRIVE, 10M
782337-20	763969-01	CP-507CDAN-20-0, MOTOR POWER CABLE, AKM MOTOR TO AKD DRIVE, 20M
782338-06	763344-06	Flex SFD Feedback Cable, AKM Motor to AKD Drive, 6M
782339-06	763362-06	Flex Motor Power Cable, AKM Motor to AKD Drive, 6M
782341-4096	782341-4096	4 GB UPGRADE/REPLACEMENT RAM FOR PXIE-8135 AND PXI-8119
782344-01	748413-01	AKM21C-CKC2C-00 PMSM Motor AC Servo, with SFD Feedback, Brake
782345-01	748420-01	AKM21C-CKC2R-00 PMSM Motor with SFD Feedback, Brake
782347-06	763393-06	Flex Motor Power Cable w/Brake, AKM Motor to AKD Drive, 6M CP-508EDBN-06-0
782347-20	763649-01	CP-508EDBN-20-0, FLEX MOTOR POWER CABLE WITH BRAKE, AKM MOTOR TO AKD DRIVE, 20M
782348-01	748425-01	AKM74Q-ANH2C-00 PMSM Motor with SFD Feedback, Brake
782365-01	748431-01	AKM21C-CKC2C-00 PMSM Motor AC Servo with SFD Feedback, Brake
782391-01	748432-01	AKM42E-ACCNR-00 PMSM Motor with SFD Feedback, Brake
782405-01	748453-01	AKM41H-ANC2C-00 PMSM Motor with SFD Feedback, Brake
782406-01	764591-01	Screw Lock Mating Connector Kit for AKD-X00306 and AKD-X00606
782407-01	152910A-01 195549A-01	NI FLEXRIO Windowed Adapter Module Enclosure (Qty 1)
782407-10	152910A-01 195549A-01	NI FLEXRIO Windowed Adapter Module Enclosure (Qty 10)
782411-01	748436-01	CS-Mount Spacer for IP Cameras
782414-01	748554-01	AKM42G-BKCN1-00 PMSM Motor with Encoder Feedback
782417-03	154363A-01	160 PIN DIN TO 4 D-SUB FOR NI PXI-2510, PXI-2520/1/2/3, PXIE-2524/5/6, AND PXIE-273X, 1M
782421-01	748481-01	AKM54L-ANCNC-00 PMSM Motor with SFD Feedback
782422-01	748477-01	Lens, 35MM, 5MP, 2/3 Inch, C-Mount, F1.4-F22, FUJINON HF35SA-1
782423-01	748478-01	Lens, 25MM, 5MP, 2/3 Inch, C-Mount, F1.4-F22, FUJINON HF25SA-1
782424-01	748479-01	Lens, 16MM, 5MP, 2/3 Inch, C-Mount, F1.4-F22, FUJINON HF16SA-1
782425-01	748480-01	Lens, 12.5MM, 5MP, 2/3 Inch, C-Mount, F1.4-F22, FUJINON HF12.5SA-1
782436-01	748485-01	MOXA AWK-3121 IEEE 802.11G Industrial Wireless Access Point
782436-02	748485-02	MOXA AWK-3121 IEEE 802.11G Industrial Wireless Access Point (International)
782436-03	748485-03	MOXA AWK-3121 IEEE 802.11G Industrial Wireless Access Point (Japan)
782446-01	154212A-01	NI FLEXRIO FPGA Module Backside Guard with Rivets
782463-01	748527-01	AKM42H-EKCNC-00 PMSM Motor with SFD Feedback, NEMA Mount
782464-01	748528-01	Single Axis AKD Drive, Analog, 6A Continuous Current, 120/240 VAC
782474-01	748505-01	2 DOF Inverted Pendulum/Gantry Crane Module, High Res Encoders, Documented Params and Control VIS

Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxxX-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
782475-01	775336-01	2 DOF Helicopter Experiment, Base Rotation Slip Ring, Documented System Parameters and Control VIS
782476-01	748506-01	2 DOF Robot Module, 4-Bar Pantograph Configuration, ABET-Aligned Lab Teaching Materials and VIS
782477-01	775337-01	3 DOF Gyro Experiment, 4 Sensed add Actuated Axes, Documented System Parameters and Control VIS
782478-01	748509-01	3 DOF HELICOPTER EXPERIMENT, YAW AXIS SLIP RING, DOCUMENTED SYSTEM PARAMS AND CONTROL VIS
782479-01	775338-01	Active Suspension Experiment, Adjustable Mass & Stiffness, ABET-Aligned Lab Teaching Materials and VIS
782481-01	775335-01	4 Channel Linear Current Amplifier, 3.5A, 27V Continuous, Current Sense, Over-Heat/Current Indication
782482-01	775329-01	Ball and Beam Module, Variable Resistance POS Feedback, ABET-Aligned Lab Teaching Materials and VIS
782483-01	748513-01	COUPLED WATER TANK EXPERIMENT, 2-TANK CONFIGURATION, DOCUMENTED SYSTEM PARAMS AND CONTROL VIS
782484-01	748514-01	DOUBLE INVERTED PENDULUM MODULE FOR IP02, DOCUMENTED SYSTEM PARAMS AND CONTROL VIS
782485-01	748515-01	DOUBLE INVERTED PENDULUM MODULE FOR SRV02-ET, DOCUMENTED SYSTEM PARAMS AND CONTROL VIS
782486-01	775330-01	Rotary Flexible Link Module, Strain Gage Flex Sense, ABET-Aligned Lab Teaching Materials and VIS
782487-01	748516-01	FLEXIBLE INVERTED PENDULUM MODULE FOR IP02 BASE, DOCUMENTED SYSTEM PARAMS AND CONTROL VIS
782488-01	748517-01	GYRO / STABLE PLATFORM MODULE FOR SRV02-ET, ABET-ALIGNED LAB TEACHING MATERIALS AND VIS
782489-01	775331-01	Linear Motion Servo Plant with Inverted Pendulum Module, ABET-Aligned Lab Teaching Materials and VIS
782490-01	748518-01	LINEAR FLEXIBLE JOINT MODULE FOR THE IP02, OPT. ENCODER, ABET-ALIGNED LAB TEACHING MATERIALS AND VIS
782491-01	748519-01	LINEAR FLEXIBLE JOINT PENDULUM MODULE FOR THE IP02, ABET ALIGNED LAB TEACHING MATERIALS AND VIS
782492-01	748520-01	MAGNETIC LEVITATION EXPERIMENT, OUTPUT CURRENT SENSE, DOCUMENTED SYSTEM PARAMS AND CONTROL VIS
782493-01	775328-01	NI-M and X-Series Terminal Board for Rapid Control Prototyping, 2 AO, 8 AI, 4 ENC IN, 8 DIO
782494-01	775325-01	Q2 USB DAQ for Real-Time Controls, 2X12BIT ADC, 2X12BIT DAC, 2XENCODER IN, 2XPWM, 8 DIO
782495-01	748521-01	Q8 USB DAQ FOR REAL-TIME CONTROLS, 8X(12BIT ADC, 12BIT DAC, ENCODER IN, PWM, DI, DO), TERMINAL BOARD
782496-01	748522-01	QPID REAL-TIME MEASUREMENT AND CONTROL DAQ, 8X(16BIT ADC, 16BIT DAC, ENC IN, PWM) 56 DIO, SPI
782497-01	748523-01	QPIDE REAL-TIME MEASUREMENT AND CONTROL DAQ, 8X(16BIT ADC, 16BIT DAC, ENC IN, PWM) 56 DIO, SPI
782498-01	775332-01	Rotary Flexible Joint Module, Adjustable Spring Stiffness, ABET Aligned Lab Teaching Materials and VIS
782499-01	775333-01	Self-Erecting Rotary Inverted Pendulum Module, ABET-Aligned Lab Teaching Materials and VIS
782500-01	748524-01	SEESAW MODULE FOR IP02, HIGH RES ENC, ANTI-BACKLASH GEARS, DOCUMENTED SYSTEM PARAMS AND CONTROL VIS
782502-01	775327-01	Rotary Servo Experiment, DC Gear-Motor, Encoder, Tach, ABET-Aligned Lab Teaching Materials and VIS
782503-01	775334-01	Remote Ball Sensor Module for BB01, ABET-Aligned Lab Teaching Materials and VIS
782504-01	748529-01	Rotary Flexible Torsion Joint Module for SRV02-ET, ABET-Aligned Lab Teaching Materials and VIS
782505-01	775326-01	1 Channel Linear Voltage Amplifier, 4.16A, 24V Continuous, Current Sense, Over-Heat/Current Indication

Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxxX-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
782509-01	748182-01	APG Mount for Smart Camera
782524-01	749409-01	SPARE/REPLACEMENT BLU-RAY DISK DRIVE FOR RMC-8355
782533-01	748543-01	AKM51L-ANCNC-00 PMSM Motor with SFD Feedback
782539-01	763357-03	CP-507CCAN-03-0 Motor Power Cable, AKM Motor to AKD Drive, 3M
782539-10	749247-01	CP-507CCAN-10-0 MOTOR POWER CABLE, AKM MOTOR TO AKD DRIVE, 10M
782539-20	749248-01	CP-507CCAN-20-0 MOTOR POWER CABLE, AKM MOTOR TO AKD DRIVE, 20M
782539-30	749672-01	CP-507CCAN-30-0 MOTOR POWER CABLE, AKM MOTOR TO AKD DRIVE, 30M
782540-01	763560-03	CF-CB7374N-03-0 Motor Feedback Cable, AKM Motor to AKD Drive, 3M
782544-01	748454-01	SPARE/REPLACEMENT AC POWER SUPPLY FOR NI RMC-8355
782545-01	748454-02	SPARE/REPLACEMENT DC POWER SUPPLY FOR NI RMC-8355
782546-01	748573-01	SPARE/REPLACEMENT FAN FOR NI RMC-8355
782551-01	748569-01	AKM24D-ANC2R-00 PMSM Motor with Resolver Feedback
782552-01	748570-01	AKM24F-ANC2R-00PMSM Motor with Resolver Feedback
782554-01	748571-01	AKM41E-NBCNC-00 Gearmotor, 25:1 Ratio, SFD Feedback
782557-01	748581-01	ICD05-075A1P3 DDL ICD Ironcore Motor, Flying Leads (100MM) with Connector
782558-01	748582-01	ICD05-075A5P3 DDL ICD Ironcore Motor, Flying Leads (100MM) with Connector
782559-01	763582-03	M1C-03, High Flex Motor Cable, 18 AWG for 3A and 6A Drives, 3M
782560-01	763583-03	H1C-03, High Flex Hall Effect Cable, 3M
782561-01	763584-01	ACI-AKD-A, AKD/DDI Motor Cable Adapter (Heidenhain-Type Encoders)
782562-01	748584-01	S77202-NANANA, Brushless Servo Drive, 72A Continuous Current, 480V
782564-01	763585-05	DE-201589, 48 AMP S700 Power Cable, 5M
782565-01	763586-05	DE-84972, Resolver Feedback Cable, 5M
782570-01	748536-01	NI 177X Smart Camera Light Bracket for AI RL4260 and RL127 Lights
782571-01	748585-01	AKM23D-ANC2R-00 PMSM Motor with Resolver Feedback, Brake
782573-01	748534-01	GPS Antenna, Magnetic Mount, 5M Cable with SMA
782574-01	154092A-10(Rev A or higher) 748535-01	GPS Antenna, Fixed Mount, 10M Cable with SMA
782575-01	748593-01	XT060-005-0-RM-60-1 XTRUE True Planetary Gearhead, Size 60, 5:1 Ratio, Size 060-1
782578-01	153105B-01	NI CAN No Termination Cable with Power Terminals, High-Speed/Low-Speed, 1M
782578-02	153105B-02	NI CAN No Termination Cable with Power Terminals, High-Speed/Low-Speed, 2M
782579-02	153105B-T2	NI CAN Single Termination Cable with Power Terminals, High-Speed, 2M
782582-01	764385-01	4-POS Screw Terminal Power Supply Plugs, High Current (Qty 5)
782596-01	154820A-01 (rev A or higher)	Dual CPU Upgrade For NI RMC-8355, Intel Xeon E5620
782598-01	748599-01	AKM74Q-ANHNC-00 PMSM Motor with SFD Feedback, No Brake
782599-01	748600-01	VT018-010-0-RM180-114 Valuetruer Planetary Gearhead, Size 018, 10:1 Ratio, Size 180 Redimount
782600-01	748601-01	Single Axis AKD Drive, ECAT, 24A Continuous Current, 240/480 VAC
782601-01	763620-01	Motor Power Cable, AKM Motor to AKD Drive, 6M, VP-508DEAN-06
782624-01	748620-01	UT014-005-0-RM142-92, Ultratrue True Planetary Gearhead, Size 014, 5:1 Ratio, Size 142 Redimount
782634-01	764722-01	Screw Lock Mating Connector Kit for AKD-X01206 (Includes X1, X2, X3, X7 AND X8 Connectors)
782636-01	748629-01	Single Axis AKD Drive, ECAT or CANOPEN, 12A Continuous Current, 120/240 VAC
782637-01	748630-01	Single Axis AKD Drive, ECAT or CANOPEN, 12A Continuous Current, 240/480 VAC
782638-01	748631-01	AKM44J-ANCNC-00 PMSM Motor with SFD Feedback
782643-01	146534B-01	NI NOX CAN MODULE INTERFACE CABLE
782671-01	748646-01	Single Axis Drive, AKD-P01206-NBAN-0000, 12A Continuous Current, 120/240VAC, Analog
782672-01	748647-01	Single Axis Drive, AKD-P02406-NBAN-0000, 24A Continuous Current, 120/240VAC, Analog
782673-01	748648-01	Single Axis Drive, AKD-P00307-NBAN-0000, 3A Continuous Current, 240/480VAC, Analog
782674-01	748649-01	Single Axis Drive, AKD-P00607-NBAN-0000, 6A Continuous Current, 240/480VAC, Analog
782675-01	748650-01	K34H-RL-LNK-NS-00 Step Motor, 4 Lead Series Connector, No Rear Shaft Ext., Straight Keyway, No Feedback
782676-01	748651-01	Single Axis DRIVE, AKD-P02407-NBAN-0000, 24A Continuous Current, 240/480VAC, Analog
782677-01	748652-01	Single Axis Drive, AKD-P01207-NBEC-0000, 12A Continuous Current, 240/480VAC, ETHERCAT
782679-01	763628-01	VP-507BEAN-09, 6 AMP AKD Power Cable, 9M

Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxX-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
782680-01	763631-01	VP-508CEAN-01, 12 AMP AKD Power Cable, 1M
782680-03	763640-01	VP-508CEAN-03, 12 AMP AKD Power Cable, 3M
782680-06	763642-01	VP-508CEAN-06, 12 AMP AKD Power Cable, 6M
782680-09	763643-01	VP-508CEAN-09, 12 AMP AKD Power Cable, 9M
782680-12	763644-01	VP-508CEAN-12, 12 AMP AKD Power Cable, 12M
782682-09	763645-01	VP-508CFAN-09, 12 AMP AKD Power/Brake Cable, 9M
782683-01	763646-01	VP-508DEAN-01, 20 AMP AKD Power Cable, 1M
782683-03	763653-01	VP-508DEAN-03, 20 AMP AKD Power Cable, 3M
782683-09	763655-01	VP-508DEAN-09, 20 AMP AKD Power Cable, 9M
782683-12	763658-01	VP-508DEAN-12, 20 AMP AKD Power Cable, 12M
782684-01	763659-01	VP-508DFAN-01, 20 AMP AKD Power/Brake Cable, 1M
782684-03	763660-01	VP-508DFAN-03, 20 AMP AKD Power/Brake Cable, 3M
782684-06	763661-01	VP-508DFAN-06, 20 AMP AKD Power/Brake Cable, 6M
782684-09	763666-01	VP-508DFAN-09, 20 AMP AKD Power/Brake Cable, 9M
782684-12	763667-01	VP-508DFAN-12, 20 AMP AKD Power/Brake Cable, 12M
782687-09	763668-01	VF-DA0474N-09, Smart Feedback (SFD) Cable, 9M
782689-01	748645-01	Q1-CRIO, Data Acquisition and Control Module for COMPACTRIO, 1 AO, 1 AI, 2 ENCODER IN
782698-01	723388-01	NI PS-10 DESKTOP POWER SUPPLY (MODEL STD-24050) 24 VDC, 5A
782703-01	762242-01	B SERIES ACCESSORIES: 4 CONNECTORS AND SCREWDRIVER
782708-01	748674-01	AKM22E-ANC2R-00 PMSM Motor with Resolver Feedback, Brake
782711-01	748675-01	AKM24D-BNBNC-00 PMSM Motor with SFD Feedback, NEMA Mount
782712-01	748676-01	NTR23-500-0-RM060-311, NEMATRU 90 Right Angle GEARHEAD, Size 023, 500:1 Ratio, Size 060 Redimount
782715-01	154928A-01 (Rev A or higher)	NI 9927, STRAIN RELIEF AND OPERATOR PROTECTION FOR 10-POS SCREW TERM (QTY 1)
782721-01	748684-01	AKM22E-CKC2R-00, PMSM Motor with Resolver Feedback, Brake
782722-01	748685-01	AKM22C-CKC2R-00, PMSM Motor with Resolver Feedback, Brake
782723-01	748686-01	AKM64K-ANC21-00, PMSM Motor with Encoder Feedback
782724-01	748687-01	AKM54H-ANCN1-00, PMSM Motor with Encoder Feedback
782730-01	748689-01	AKM54G-V5C2C-00 GEARMOTOR, 115MM Frame, 5:1 Reduction Ratio, 24VDC Brake, SFD Feedback
782731-01	748693-01	AKM23D-ACC2R-00, PMSM Motor with Resolver Feedback, Brake
782732-01	748694-01	AKM22E-ACC2R-00, PMSM Motor with Resolver Feedback, Brake
782733-01	748695-01	AKM22C-ACC2R-00, PMSM Motor with Resolver Feedback, Brake
782765-01	763849-01	CABLE ASSEMBLY, USB A TO MINI ADAPTER CABLE, 0.1M
782769-01	154812B-8R7 (rev B or higher)	CABLE ASSEMBLY, SMA-M TO SMA-F BULKHEAD, 0.2M
782770-01	156923A-01 (Rev A or higher)	CABLE ASSEMBLY, SMA TO SMA, 1M
782778-01	748837-01	USRP RACK MOUNT KIT (COMBINE 4 DEVICES INTO 3U, 19" RACK)
782781-01	156923A-01 764897-01	SMA CABLE AND 30DB ATTENUATOR LOOP BACK KIT - ETTUS RESEARCH
782786-01	697211-02	16GB INDUSTRIALLY RATED COMPACT FLASH CARD FOR TPC-22XX
782801-01	611484-01	EMI SUPPRESSION FERRITE FOR NI 9229/39 BNC (QTY 1)
782803-01	711627-01	EMI SUPPRESSION FERRITE FOR NI 9401 (QTY 1)
782805-01	748713-01	AKM24D-N5BNC-00, PMSM Gearmotor, 5:1 Reduction Ratio, SFD Feedback
782818-01	155225A-01 (rev A or higher)	PANEL MOUNTING KIT FOR NI 9155
782839-01	762008-01	2-TERMINAL DETACHABLE SCREW-TERMINAL FOR PXIE-4610
782847-01	748749-01	AKM33E-ANC2C-00, PMSM MOTOR, 24VDC BRAKE, SFD FEEDBACK
782848-01	748752-01	Replacement System Monitor Assembly For NI PXI-1016 Chassis
782850-01	151611A-01 (rev A or higher) 154048A-01 (rev A or higher) 154050A-01 (rev A or higher) 763282-07	NI PXIE-5667 7 GHZ SPECTRAL MONITORING RECEIVER CABLE KIT
782851-01	151611A-01 (rev A or higher) 154048A-01 (rev A or higher) 154049A-01 (rev A or higher) 763282-07	NI PXIE-5667 3.6 GHZ SPECTRAL MONITORING RECEIVER CABLE KIT

Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxxX-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
782854-01	153700A-01(Rev A or higher)	NI HDD-8266 24-DRIVE, 24TB SATA, CABLED PCIE HDD ENCLOSURE W/RAID
782855-01	748750-01	AKM32E-ANC2C-00, PMSM MOTOR, 24VDC BRAKE, SFD FEEDBACK
782858-01	153700A-02	NI HDD-8266 24-DRIVE, 3.5TB SAS, CABLED PCIE HDD ENCLOSURE W/RAID
782863-01	155391C-01 (rev C or higher)	PANEL MOUNT KIT FOR 8 SLOT COMPACTRIO 906X SYSTEMS
782866-01	764845-01	NI TBX-50B, 50 PIN DSUB SCREW TERMINAL BLOCK
782876-01	748754-01	KBM-57S01-A00 Frameless Brushless Servomotor, Stack Length 01, A Winding
782877-01	748757-01	AKM43G-VAC2C-00, AKM Gearmotor, Precision Line Gearhead, 10:1 Ratio SFD Feedback, 24VDC Brake
782879-01	748763-01	AKM43L-ANC2C-00, PMSM MOTOR, 24 VDC BRAKE, SFD FEEDBACK
782883-01	748764-01	AKM65L-ANCNC-00 PMSM Motor, 90° Intercontec Connectors, No Brake, SFD Feedback
782887-01	154915A-01 (rev A or higher) 764763-01	ADDITIONAL CONNECTOR KIT FOR NI PXIE-4112/13 POWER SUPPLIES
782908-01	748771-01	AKM42E-EKGNR-01, PMSM MOTOR, NO BRAKE, RESOLVER FEEDBACK
782909-01	152190A-01(Rev A or higher)	HIGH SPEED USB - 1 METER CABLE - MICRO TO STD MALE
782909-02	152190A-02 (rev A or higher)	HIGH SPEED USB - 2 METER CABLE - MICRO TO STD MALE
782910-01	748772-01	AKM41E-VBCNC-00, AKM GEARMOTOR, PRECISION LINE GEARHEAD, 100MM FRAME, 25:1 RATIO, SFD FEEDBACK
782911-2048	697464-2048	Replacement/Upgrade 2 GB Of DDR3 RAM For PXI(E)-8115 Controllers
782911-4096	697464-4096	Replacement/Upgrade 4 GB Of DDR3 RAM For PXI(E)-8115 Controllers
782926-01	748781-01	AKM43L-EKC2C-00, PMSM MOTOR, 24 VDC BRAKE, SFD FEEDBACK
782927-01	748783-01	AKM65P-GCCNC-01, PMSM MOTOR, NO BRAKE, SFD FEEDBACK
782928-01	748784-01	AKM51H-ACCNC-01, PMSM MOTOR, NO BRAKE, SFD FEEDBACK
782933-12	763839-12	CF-SS-CHUE-12 COMMUTATING ENCODER FEEDBACK CABLE, AKM MOTOR TO AKD DRIVE, 12M
782936-01	748794-01	CAMERA, BASLER RACER, RAL2048-48GM, 2048 PIXELS, 48 KHZ, MONOCHROME
782937-01	748795-01	CAMERA, BASLER RACER, RAL4096-24GM, 4096 PIXELS, 24 KHZ, MONOCHROME
782938-01	748796-01	CAMERA, BASLER RACER, RAL6144-16GM, 6144 PIXELS, 16 KHZ, MONOCHROME
782939-01	748797-01	CAMERA, BASLER RACER, RAL8192-12GM, 8192 PIXELS, 12 KHZ, MONOCHROME
782940-01	748798-01	CAMERA, BASLER RACER, RAL12288-8GM, 12288 PIXELS, 8 KHZ, MONOCHROME
782941-01	748799-01	CAMERA, BASLER RACER, RAL2048-80KM, 2048 PIXELS, 80 KHZ, MONOCHROME
782942-01	748800-01	CAMERA, BASLER RACER, RAL4096-80KM, 4096 PIXELS, 80 KHZ, MONOCHROME
782943-01	748801-01	CAMERA, BASLER RACER, RAL6144-80KM, 6144 PIXELS, 80 KHZ, MONOCHROME
782944-01	748802-01	CAMERA, BASLER RACER, RAL8192-80KM, 8192 PIXELS, 80KHZ, MONOCHROME
782945-01	748803-01	CAMERA, BASLER RACER, RAL12288-66KM, 12288 PIXELS, 66 KHZ, MONOCHROME
782948-01	155086A-01(Rev A or higher)	I/O Accessory For NI 8237R And 3M 26-PIN D-SUB Cable
782949-01	194646B-01 (rev B or higher)	FAN FILTERS FOR PXI AND PXI EXPRESS CHASSIS
782950-01	763438-01	DC POWER CORD FOR PXIE-1082DC
782964-10	749251-01	CF-DA0374N-10-0, MOTOR SFD FEEDBACK CABLE, AKM MOTOR TO AKD DRIVE, 10M
782964-20	749250-01	CF-DA0374N-20-0, MOTOR FEEDBACK CABLE, AKM MOTOR TO AKD DRIVE, 20M
782987-01	748831-01	22in. Widescreen IPS Monitor - Displayport, HDMI, DVI, Abd VGA Input For PC'S
782988-01	748830-01	19in. Flat Panel Monitor- Displayport, DVI, And VGA Input For PC'S
782989-01	763844-01	1.8M DISPLAYPORT TO DISPLAYPORT CABLE
783001-8192	697464-8192	8 GB UPGRADE/REPLACEMENT RAM FOR PXIE-8840
783013-01	748903-01	STEPPER DRIVE, 120VAC SUPPLY, TWO-PHASE, BIPOLAR STEP MOTORS, 0.5-5A/PHASE, ENCODER FEEDBACK
783014-01	748904-01	STEPPER DRIVE, 220VAC SUPPLY, TWO-PHASE, BIPOLAR STEP MOTORS, 0.5-2.55A/PHASE, ENCODER FEEDBACK
783015-01	748900-01	STEPPER DRIVE, 12-48VDC SUPPLY, 0.3-2.2 A/PHASE, STEP & DIRECTION, 2-PHASE STEP MOTORS
783016-01	748901-01	STEPPER DRIVE, 24-48VDC SUPPLY, 1.12-4.5 A/PHASE, STEP & DIRECTION, 2-PHASE STEP MOTORS
783017-01	748902-01	STEPPER DRIVE, 24-75VDC SUPPLY, 2.35-8.0 A/PHASE, STEP & DIRECTION, 2-PHASE STEP MOTORS
783021-01	748908-01	REGENERATION CLAMP FOR DC-INPUT DRIVES, 50W CONTINUOUS, 800W PEAK
783022-01	748991-01	INCREMENTAL ENCODER FOR NEMA 17 STEP MOTORS. 5MM HUB DIA, 2000 CPR, DIFFERENTIAL OUTPUTS

Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxxX-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
783023-01	748992-01	INCREMENTAL ENCODER FOR NEMA 23 & 24 STEP MOTORS. 1/4" HUB DIA, 2000 CPR, DIFFERENTIAL OUTPUTS
783024-01	748993-01	INCREMENTAL ENCODER FOR NEMA 34 STEP MOTORS. 3/8" HUB DIA, 2000 CPR, DIFFERENTIAL OUTPUTS
783025-01	748994-01	ENCODER CABLE, 10FT, SMD-762X STEPPER DRIVES TO ENC-774X INCREMENTAL ENCODERS
783027-01	748909-01	ST8-1 HYBRID STEP MOTOR, 2-PHASE, NEMA 8, 1.8 DEG/STEP, 2.4 OZ-IN
783027-02	748910-01	ST8-1D HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 8, 2.4 OZ-IN, DUAL SHAFT
783028-01	748911-01	ST8-2 HYBRID STEP MOTOR, 2-PHASE 1.8 DEG/STEP, NEMA 8, 4.44 OZ-IN
783028-02	748912-01	ST8-2D HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 8, 4.44 OZ-IN, DUAL SHAFT
783029-01	748913-01	ST11-1 HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 11, 7.4 OZ-IN
783029-02	748914-01	ST11-1D HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 11, 7.4 OZ-IN, DUAL SHAFT
783030-01	748915-01	ST11-2 HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 11, 15.3 OZ-IN
783030-02	748916-01	ST11-2D HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 11, 15.3 OZ-IN, DUAL SHAFT
783031-01	748917-01	ST14-1 HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 14, 26 OZ-IN
783031-02	748918-01	ST14-1D HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 14, 26 OZ-IN, DUAL SHAFT
783032-01	748919-01	ST17-1 HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 17, 31.2 OZ-IN
783032-02	748920-01	ST17-1D HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 17, 31.2 OZ-IN, DUAL SHAFT
783032-03	748921-01	ST17-1E HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 17, 31.2 OZ-IN, W/ ENCODER
783033-01	748922-01	ST17-2 HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 17, 52.4 OZ-IN
783033-02	748923-01	ST17-2D HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 17, 52.4 OZ-IN, DUAL SHAFT
783033-03	748924-01	ST17-2E HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 17, 52.4 OZ-IN, W/ ENCODER
783034-01	748925-01	ST17-3 HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 17, 77.9 OZ-IN
783034-02	748926-01	ST17-3D HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 17, 77.9 OZ-IN, DUAL SHAFT
783034-03	748927-01	ST17-3E HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 17, 77.9 OZ-IN, W/ ENCODER
783035-01	748928-01	ST17-4 HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 17, 113 OZ-IN
783035-02	748929-01	ST17-4D HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 17, 113 OZ-IN, DUAL SHAFT
783035-03	748930-01	ST17-4E HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 17, 113 OZ-IN, W/ ENCODER
783036-01	748931-01	ST23-1 HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 23, 76.5 OZ-IN
783036-02	748932-01	ST23-1D HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 23, 76.5 OZ-IN, DUAL SHAFT
783036-03	748933-01	ST23-1E HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 23, 76.5 OZ-IN, W/ ENCODER
783037-01	748934-01	ST23-2 HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 23, 76.5 OZ-IN
783037-02	748935-01	ST23-2D HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 23, 76.5 OZ-IN, DUAL SHAFT
783037-03	748936-01	ST23-2E HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 23, 76.5 OZ-IN, W/ ENCODER
783038-01	748937-01	ST23-3 HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 23, 84.4 OZ-IN
783038-02	748938-01	ST23-3D HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 23, 84.4 OZ-IN, DUAL SHAFT
783038-03	748939-01	ST23-3E HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 23, 84.4 OZ-IN, W/ ENCODER
783039-01	748940-01	ST23-4 HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 23, 158 OZ-IN
783039-02	748941-01	ST23-4D HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 23, 158 OZ-IN, DUAL SHAFT
783039-03	748942-01	ST23-4E HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 23, 158 OZ-IN, W/ ENCODER
783040-01	748943-01	ST23-5 HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 23, 167 OZ-IN
783040-02	748944-01	ST23-5D HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 23, 167 OZ-IN, DUAL SHAFT

Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxxX-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
783040-03	748945-01	ST23-5E HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 23, 167 OZ-IN, W/ ENCODER
783041-01	748946-01	ST23-6 HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 23, 269 OZ-IN
783041-02	748947-01	ST23-6D HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 23, 269 OZ-IN, DUAL SHAFT
783041-03	748948-01	ST23-6E HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 23, 269 OZ-IN, W/ ENCODER
783042-01	748949-01	ST23-7 HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 23, 255 OZ-IN
783042-02	748950-01	ST23-7D HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 23, 255 OZ-IN, DUAL SHAFT
783042-03	748951-01	ST23-7E HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 23, 255 OZ-IN, W/ ENCODER
783043-01	748952-01	ST23-8 HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 23, 354 OZ-IN
783043-02	748953-01	ST23-8D HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 23, 354 OZ-IN, DUAL SHAFT
783043-03	748954-01	ST23-8E HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 23, 354 OZ-IN, W/ ENCODER
783044-01	748955-01	ST24-1 HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 24, 123 OZ-IN
783044-02	748956-01	ST24-1D HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 24, 123 OZ-IN, DUAL SHAFT
783044-03	748957-01	ST24-1E HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 24, 123 OZ-IN, ENCODER
783045-01	748958-01	ST24-2 HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 24, 177 OZ-IN
783045-02	748959-01	ST24-2D HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 24, 177 OZ-IN, DUAL SHAFT
783045-03	748960-01	ST24-2E HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 24, 177 OZ-IN, W/ ENCODER
783046-01	748961-01	ST24-3 HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 24, 354 OZ-IN
783046-02	748962-01	ST24-3D HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 24, 354 OZ-IN, DUAL SHAFT
783046-03	748963-01	ST24-3E HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 24, 354 OZ-IN, W/ ENCODER
783047-01	748964-01	ST34-1 HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 34, 397 OZ-IN
783047-02	748965-01	ST34-1D HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 34, 397 OZ-IN, DUAL SHAFT
783047-03	748966-01	ST34-1E HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 34, 397 OZ-IN, W/ ENCODER
783048-01	748967-01	ST34-2 HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 34, 555 OZ-IN
783048-02	748968-01	ST34-2D HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 34, 555 OZ-IN, DUAL SHAFT
783048-03	748969-01	ST34-2E HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 34, 555 OZ-IN, W/ ENCODER
783049-01	748970-01	ST34-3 HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 34, 555 OZ-IN
783049-02	748971-01	ST34-3D HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 34, 555 OZ-IN, DUAL SHAFT
783049-03	748972-01	ST34-3E HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 34, 555 OZ-IN, W/ ENCODER
783050-01	748973-01	ST34-4 HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 34, 850 OZ-IN
783050-02	748974-01	ST34-4D HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 34, 850 OZ-IN, DUAL SHAFT
783050-03	748975-01	ST34-4E HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 34, 850 OZ-IN, W/ ENCODER
783051-01	748976-01	ST34-5 HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 34, 1110 OZ-IN
783051-02	748977-01	ST34-5D HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 34, 1110 OZ-IN, DUAL SHAFT
783051-03	748978-01	ST34-5E HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 34, 1110 OZ-IN, W/ ENCODER
783052-01	748979-01	ST34-6 HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 34, 1110 OZ-IN
783052-02	748980-01	ST34-6D HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 34, 1110 OZ-IN, DUAL SHAFT
783052-03	748981-01	ST34-6E HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 34, 1110 OZ-IN, W/ ENCODER
783053-01	748982-01	ST34-7 HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 34, 1260 OZ-IN
783053-02	748983-01	ST34-7D HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 34, 1260 OZ-IN, DUAL SHAFT
783053-03	748984-01	ST34-7E HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 34, 1260 OZ-IN, W/ ENCODER
783054-01	748985-01	ST34-8 HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 34, 1694 OZ-IN

Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxxX-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
783054-02	748986-01	ST34-8D HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 34, 1694 OZ-IN, DUAL SHAFT
783054-03	748987-01	ST34-8E HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 34, 1694 OZ-IN, W/ ENCODER
783055-01	748988-01	ST34-9 HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 34, 1694 OZ-IN
783055-02	748989-01	ST34-9D HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 34, 1694 OZ-IN, DUAL SHAFT
783055-03	748990-01	ST34-9E HYBRID STEP MOTOR, 2-PHASE, 1.8 DEG/STEP, NEMA 34, 1694 OZ-IN, W/ ENCODER
783057-01	748891-01	ISM-7400 NEMA 17 INTEGRATED STEPPER DRIVE+MOTOR, STEP & DIR, 68 OZ-IN, SINGLE SHAFT
783057-02	748892-01	ISM-7400D NEMA 17 INTEGRATED STEPPER DRIVE+MOTOR, STEP & DIR, 68 OZ-IN, DUAL SHAFT
783057-03	748893-01	ISM-7400E NEMA 17 INTEGRATED STEPPER DRIVE+MOTOR, STEP & DIR, 68 OZ-IN, W/ ENCODER
783058-01	748894-01	ISM-7401 NEMA 23 INTEGRATED STEPPER DRIVE+MOTOR, STEP & DIR, 125 OZ-IN, SINGLE SHAFT
783058-02	748895-01	ISM-7401D NEMA 23 INTEGRATED STEPPER DRIVE+MOTOR, STEP & DIR, 125 OZ-IN, DUAL SHAFT
783058-03	748896-01	ISM-7401E NEMA 23 INTEGRATED STEPPER DRIVE+MOTOR, STEP & DIR, 125 OZ-IN, WITH ENCODER
783059-01	748897-01	ISM-7402 NEMA 23 INTEGRATED STEPPER DRIVE+MOTOR, STEP & DIR, 210 OZ-IN, SINGLE SHAFT
783059-02	748898-01	ISM-7402D NEMA 23 INTEGRATED STEPPER DRIVE+MOTOR, STEP & DIR, 210 OZ-IN, DUAL SHAFT
783059-03	748899-01	ISM-7402E NEMA 23 INTEGRATED STEPPER DRIVE+MOTOR, STEP & DIR, 210 OZ-IN, WITH ENCODER
783060-01	748875-01	AKM24D-ANCNDB00, PMSM MOTOR, W/O BRAKE, MULTI-TURN ABSOLUTE ENDAT ENCODER
783061-01	748876-01	AKM24D-ANC2DB00, PMSM MOTOR, 24V DC BRAKE, MULTI-TURN ABSOLUTE ENDAT ENCODER
783075-01	748153-01	VERT2450 VERTICAL ANTENNA (2.4-2.5 AND 4.9-5.9 GHZ) DUALBAND
783077-01	748884-01	3YLN-06 MOTOR CABLE CHOKE, 6 AMP CONTINUOUS OR LESS
783079-01	748885-01	XT120-020-0-RM115-71 XTRUE TRUE PLANETARY GEARHEAD, SIZE 120, 20:1 RATIO, SIZE 115 REDIMOUNT
783085-01	748887-01	P70530-PNN DRIVE, 20-75 VDC, 5 AMP CONT, MOTION NODE INDEXING, NO FEEDBACK DEVICE SUPPORT
783089-01	155367A-01L (rev A or higher) 155404A-01 (rev A or higher)	NI 5549 DC POWER ACCESSORY CCA
783094-01	156514A-01(Rev A or higher)	NI 9967, STRAIN RELIEF AND OPERATOR PROTECTION FOR NI 9242 (QTY 1)
783099-01	749158-01	SISU 1004 4-AXIS STEPPER MOTOR INTERFACE MODULE FOR CRIO
783104-01	749004-01	AKM51G-ANG2C-00 PMSM Motor, SFD Feedback, w/Brake
783105-01	749005-01	Single Axis AKD Drive, ECAT or CANOPEN, 6A Continues Current, 120/240 VAC
783125-01	749097-01	BASLER ACE CAMERA, AC2040-25GM NIR, 2048 X 2048, 25 FPS, MONOCHROME, NEAR INFRARED
783136-01	155936A-01(Rev A or higher)	NI WTS RACK MOUNT KIT
783137-01	749084-01	VLM32H-CLNC-00, BRUSHLESS SERVO, METRIC MOUNT, SMOOTH SHAFT, FLYING LEAD CABLES, SMART FEEDBACK, 1 M LEADS
783140-01	749085-01	AKM23D-ANB2R-00 PMSM MOTOR, SMOOTH SHAFT, 24 VDC BRAKE, RESOLVER.
783141-01	749086-01	AKM23D-CKB2R-00 PMSM MOTOR, OPEN KEYWAY, 24 VDC BRAKE, RESOLVER.
783142-01	749087-01	AKM21C-ANB2R-00 PMSM MOTOR, SMOOTH SHAFT, 24 VDC BRAKE, RESOLVER.
783143-01	749088-01	AKM21C-CKB2R-00 PMSM MOTOR, OPEN KEYWAY, 24 VDC BRAKE, RESOLVER.
783154-01	156516A-01(Rev A or higher)	NI 9969, STRAIN RELIEF AND OPERATOR PROTECTION FOR NI 9244 (QTY 1)
783158-01	763946-01	CP-508DCAN-06-0, FLEX MOTOR POWER CABLE W/BRAKE, AKM MOTOR TO AKD DRIVE, 6M
783159-01	763947-01	CF-SB7374N-06-0, FLEX MOTOR FEEDBACK CABLE, AKM MOTOR TO AKD DRIVE, 6M
783159-30	749673-01	CF-SB7374N-30-0, FLEX MOTOR FEEDBACK CABLE, AKM MOTOR TO AKD DRIVE, 30M

Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxxX-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
783160-01	749107-01	AKD SERIES BRUSHLESS SERVO DRIVE, RATED 12 A CONTINUOUS 240/480 VAC 3 PHASE, WITH ANALOG COMMAND
783161-01	749108-01	AKD SERIES BRUSHLESS SERVO DRIVE, RATED 24 A CONTINUOUS 240/480 VAC 3 PHASE, WITH ANALOG COMMAND
783162-01	749109-01	AKM54K-V4CNC-00 BLDC GEARMOTOR, 115 MM FRAME, 4:1 REDUCTION RATIO, SFD FEEDBACK
783163-01	749110-01	AKM64P-V4CNC-01 BLDC GEARMOTOR, 142 MM FRAME, 4:1 REDUCTION RATIO, SFD FEEDBACK
783164-01	749111-01	AKM63N-VACNC-01 BLDC GEARMOTOR, 142 MM FRAME, 10:1 REDUCTION RATIO, SFD FEEDBACK
783165-01	749112-01	AKM74P-ACCNC-01 PMSM MOTOR WITH SFD FEEDBACK
783166-01	749159-01	SISU RJ45 TO TERMINALS BREAKOUT FOR THE SISU-1004 C SERIES MODULE
783171-01	749114-01	KOLLMORGEN KCM-E200 CAPACITOR MODULE
783172-01	749115-01	KOLLMORGEN KCM-E400 CAPACITOR MODULE
783176-01	749117-01	AKM24D-ANBND-00 PMSM MOTOR, INTERCONTEC CONNECTOR, OPTICAL ENCODER
783177-01	749118-01	AKM44H-ANCND-00 PMSM MOTOR, INTERCONTEC CONNECTOR, OPTICAL ENCODER
783178-01	749119-01	AKM63L-ANCND-00 PMSM MOTOR, INTERCONTEC CONNECTOR, OPTICAL ENCODER
783179-01	749120-01	AKM62P-ANCND-00 PMSM MOTOR, INTERCONTEC CONNECTOR, OPTICAL ENCODER
783180-01	749121-01	AKM74P-ANCND-00 PMSM MOTOR, INTERCONTEC CONNECTOR, OPTICAL ENCODER
783181-01	749122-01	AKM83T-ANTND-00 PMSM MOTOR, IP67 TERMINAL BOX, OPTICAL ENCODER
783189-01	749129-01	AKM24D-ANCNC-00 PMSM MOTOR, INTERCONTEC CONNECTORS, SFD FEEDBACK
783190-01	749130-01	XT80-030-0-RM090-6, XTRUE GEARHEAD, SIZE 80, 30:1 RATIO, 090 REDIMOUNT
783195-01	783195-01	SFP 1 GIGABIT ETHERNET INTERFACE KIT - ETTUS RESEARCH
783196-01	152117B-01	USRP X3XX 1U RACK MOUNT (2 USRP X300 DEVICES)
783197-01	749138-01	XT60-020-0-RM060-6, XTRUE GEARHEAD, SIZE 60, 20:1 RATIO, 060 REDIMOUNT
783199-01	747969-250	250GB 7200RPM HDD FOR PXI EMBEDDED CONTROLLERS
783202-01	749143-01	AKM24D-ANB2R-00 PMSM MOTOR, INTERCONTEC CONNECTORS, 24 VDC BRAKE, RESOLVER
783203-01	749144-01	AKM24F-ANB2R-00 PMSM MOTOR, INTERCONTEC CONNECTORS, 24 VDC BRAKE, RESOLVER
783204-01	763978-01	CF-RA2574N-20-0 MOTOR FEEDBACK CABLE, AKM MOTOR TO AKD DRIVE, 20M
783205-01	154469B-01	SPARE/REPLACEMENT REMOVABLE HARD DRIVE SHUTTLE FOR NI PXIE-8135
783270-01	749145-01	AKM12C-AKCNC-01 PMSM MOTOR, INTERCONTEC CONNECTORS, W/O BRAKE, SFD FEEDBACK
783273-01	749154-01	TRIPOD ADAPTER PLATE, BASLER RACER SERIES
783274-01	749155-01	C-MOUNT LENS ADAPTER, BASLER RACER SERIES
783275-01	749156-01	F-MOUNT LENS ADAPTER, BASLER RACER SERIES
783276-01	763980-01	I/O CABLE, 12-PIN HIROSE TO BARE WIRES, 10 METERS, RACER AND RUNNER CAMERAS
783277-01	763982-01	POWER CABLE, 6-PIN HIROSE TO BARE WIRE, 10 METERS, BASLER SPRINT AND RACER CAMERAS
783286-01	749162-01	AKM64L-ANCNC-00 PMSM MOTOR, SMOOTH SHAFT, W/O BRAKE, SMART FEEDBACK
783297-01	749169-01	BASLER SCOUT CAMERA, SCA1300-32GM 90 DEGREE, 1296 X 966, 32 FPS, MONOCHROME
783301-01	749175-01	AKM43L-ANCNAB-0F PMSM MOTOR, INTERCONTEC CONNECTOR, BISS ENCODER, FOOD GRADE
783302-01	749187-01	AKM62L-ACC2R-01 PMSM MOTOR, RESOLVER, 24 VDC BRAKE, SHAFT SEAL
783312-01	749194-01	VLM22C-DKNC-00 BRUSHLESS SERVO, NEMA 23 MOUNT, 1/4" SMOOTH SHAFT, SMART FEEDBACK, 1 M LEADS
783313-01	749203-01	AKM23C-ANG2AB-01 PMSM MOTOR, INTERCONTEC CONNECTORS, 24 VDC BRAKE, BISS SINE ENCODER, SHAFT SEAL
783314-01	749204-01	AKM53L- ANG2AB-01 PMSM MOTOR, INTERCONTEC CONNECTORS, 24 VDC BRAKE, BISS SINE ENCODER, SHAFT SEAL
783315-01	749205-01	AKM74Q- ANH2AB-01 PMSM MOTOR, INTERCONTEC CONNECTORS, 24 VDC BRAKE, BISS SINE ENCODER, SHAFT SEAL
783316-01	749206-01	AKM43H- ANG2AB-01 PMSM MOTOR, INTERCONTEC CONNECTORS, 24 VDC BRAKE, BISS SINE ENCODER, SHAFT SEAL
783317-01	749207-01	AKM33C-ANG2AB-01 PMSM MOTOR, INTERCONTEC CONNECTORS, 24 VDC BRAKE, BISS SINE ENCODER, SHAFT SEAL

Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxxX-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
783319-01	763200-01	ENCODER FEEDBACK CABLE, CF-SB7374N-20, AKM MOTOR TO AKD DRIVE, 20 M
783321-01	749212-01	FILTER, DE-201569, 3NF-07
783322-01	749213-01	FILTER, DE-201570 3NF-16
783323-01	749214-01	FILTER, DE-201571 3NF-30
783324-01	749209-01	SERVO DRIVE EXTERNAL RESISTOR, BAR-500-33, 500 W, 33 OHMS
783325-01	749210-01	SERVO DRIVE EXTERNAL RESISTOR, BAS-4000-23, 4000 W, 23 OHMS
783326-01	749211-01	SERVO DRIVE EXTERNAL RESISTOR, BAR-1500-33, 1500 W, 33 OHMS
783327-01	156047A-01(Rev A or higher) 156084A-03(Rev A or higher)	CVS I/O ACCESSORY AND 44-PIN HDSUB MALE TO 44-PIN HDSUB FEMALE 3 METER CABLE
783328-01	156047A-01 (rev A or higher) 156084A-0R5 (rev A or higher)	CVS I/O ACCESSORY AND 44-PIN HDSUB MALE TO 44-PIN HDSUB FEMALE .5 METER CABLE
783329-10	156993A-10(Rev A or higher)	X8 MXI-EXPRESS FIBER CABLE (X4 GEN2 SPEED), 10M
783329-100	156993A-100(Rev A or higher)	X8 MXI-EXPRESS FIBER CABLE (X4 GEN2 SPEED), 100M
783337-01	749224-01	AKM24F-ANB2C-00 PMSM MOTOR, 24VDC BRAKE, SFD FEEDBACK
783342-01	763990-0R5	10 GIGABIT SFP+ ETHERNET CABLE, 0.5M - ETTUS RESEARCH
783343-01	763990-01	10 GIGABIT SFP+ ETHERNET CABLE, 1 M - ETTUS RESEARCH
783344-01	763990-03	10 GIGABIT SFP+ ETHERNET CABLE, 3 M - ETTUS RESEARCH
783349-01	723535-01 763864-01	12 VOLT POWER SUPPLY FOR USRP X3XX US POWER CORD
783368-01	783368-01	GPIO-USB-HS+, WITH NI-488.2 FOR WINDOWS
783372-01	749246-01	AKM33H-ANC2C-00 PMSM MOTOR, 24VDC BRAKE, SFD FEEDBACK
783374-01	749244-01	AKM63K-ANC22-00 PMSM MOTOR, 24VDC BRAKE, 2048 LPR COMMUTATING ENCODER
783375-01	749245-01	AKM53M-CNCN2-00 PMSM MOTOR, SMOOTH SHAFT, 2048 LPR COMMUTATING ENCODER
783384-01	749254-01	NTR34-006-0-RM090-40, NEMATRU 90 RIGHT ANGLE GEARHEAD, SIZE 34, 6:1 RATIO, SIZE 090 REDIMOUNT
783386-01	749276-01	KBMS-17H02-A00 SERVOMOTOR, HIGH VOLTAGE INSULATION, STACK LENGTH 02, A WINDING
783387-01	749277-01	KBMS-17H02-D00 SERVOMOTOR, HIGH VOLTAGE INSULATION, STACK LENGTH 02, D WINDING
783388-01	749278-01	KBMS-17H03-A00 SERVOMOTOR, HIGH VOLTAGE INSULATION, STACK LENGTH 03, A WINDING
783389-01	749279-01	KBMS-25H03-D00 SERVOMOTOR, HIGH VOLTAGE INSULATION, STACK LENGTH 03, D WINDING
783390-01	749280-01	S20330-VTS SERVO DRIVE, 90 VDC, 3 AMP CONTINUOUS, SMART FEEDBACK DEVICE AND HALLS SUPPORT
783391-01	749281-01	S20630-VTS SERVO DRIVE, 90 VDC, 6 AMP CONTINUOUS, SMART FEEDBACK DEVICE AND HALLS SUPPORT
783428-01	749311-01	AKM23F-ANB2C-00 PMSM MOTOR, INTERCONTEC CONNECTORS, 24 VDC BRAKE, SMART FEEDBACK
783434-01	749317-01	AKM22C-ANB2LB-00 BRUSHLESS SERVO, 24 VDC BRAKE, ENDAT ENCODER
783436-01	749319-01	AKM33E-ANC2LB-00 BRUSHLESS SERVO, 24 VDC BRAKE, ENDAT ENCODER
783438-01	763112-01	CF-SB7374N-03-0 MOTOR FEEDBACK CABLE, ENDAT ENCODER, FLEXING, 3M
783439-01	749321-01	D083M-22-1310 HOUSED DDR 230V BRUSHLESS SERVOMOTOR, SINGLE TURN ABSOLUTE SINE ENCODER (2048 LINE)
783469-01	156923A-01 (Rev A or higher)	CABLE ASSEMBLY, SMA TO SMA, 1M
783480-01	748534-01	5V GPS ANTENNA, MAGNETIC MOUNT, 5M CABLE WITH SMA – ETTUS RESEARCH
783488-01	195994A-03 (Rev A or higher)	CABLE ASSEMBLY, MXI-EXPRESS, X4, 3M
783492-01	152117B-01 (Rev B or higher) 740275-01 741802-01 743157-01	USRP RIO 1U RACK MOUNT (2 USRP RIO DEVICES)
783497-01	749391-01	CAMERA, BASLER ACE, ACA1920-25UM, 1920 X 1080, 25 FPS, MONOCHROME
783498-01	749392-01	CAMERA, BASLER GIGE ACE, ACA1600-60GM, 1600 X 1200, 60 FPS, MONOCHROME
783499-01	749393-01	CAMERA, BASLER ACE, ACA3800-14UM, 3840 X 2748, 14 FPS, MONOCHROME
783500-01	749394-01	CAMERA, BASLER ACE, ACA3800-14UC, 3840 X 2748, 14 FPS, COLOR

Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxxX-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
783501-01	749395-01	CAMERA, BASLER ACE, ACA4600-10UC, 4608 X 3288, 10 FPS, COLOR
783509-01	749398-01	CAMERA, BASLER GIGE ACE, ACA1600-60GM, 1600 X 1200, 60 FPS, MONOCHROME
783510-01	749399-01	CAMERA, BASLER ACE, ACA1600-60GC, 1600 X 1200, 60 FPS, COLOR
783511-01	749400-01	CAMERA, BASLER ACE, ACA1280-60GM, 1280 X 1024, 60 FPS, MONOCHROME
783512-01	749401-01	CAMERA, BASLER ACE, ACA1280-60GC, 1280 X 1024, 60 FPS, COLOR
783518-01	749403-01	CAMERA, BASLER ACE, ACA1920-25GM, 1920 X 1080, 25 FPS, MONOCHROME
783519-01	749404-01	CAMERA, BASLER ACE, ACA1920-25GC, 1920 X 1080, 25 FPS, COLOR
783529-01	156361A-01(Rev A or higher)	NI 9978 4-POS GOLD POWER SUPPLY PLUGS (QTY 5)
783538-01	157206A-01(Rev A or higher)	VIRTUALBENCH BINDING POST ADAPTER
783565-01	764714-01 764715-01	VIRTUALBENCH ACCESSORY KIT: 1 DIO CONNECTOR, 1 PWS CONNECTOR, 1 SCREWDRIVER
783569-01	156783A-01(Rev A or higher)	VIRTUALBENCH DESKTOP MOUNTING KIT
783592-01	749503-01	SMD-7622 STEPPER DRIVE, 120VAC, TWO-PHASE BIPOLAR STEP MOTORS, 0.5-5A/PHASE, ENCODER FEEDBACK
783606-01	749491-01	D063M-12-1310 HOUSED DDR SERIES 230V BRUSHLESS SERVOMOTOR, ABSOLUTE SINE ENCODER (2048 LINE)
783644-01	749539-01	CAMERA, BASLER SCOUT, SCA1300-32FM 90 DEGREE, 1296 X 966, 32 FPS, MONO, 90 DEGREE HOUSING
783646-01	151612A-01(Rev A or higher) 154048A-01(Rev A or higher) 763187-01 763282-07	NI PXIE-5667 3.6 GHZ MIMO CABLE KIT
783648-01	763199-01	NI PXIE 5667 MULTI-CHASSIS MIMO CABLE KIT
783654-01	749549-01	VT075-050-0-RM075-40, VALUETRUE HELICAL TRUE PLANETARY GEARHEAD, SIZE 075, 50:1 RATIO, SIZE 075
783658-01	749560-01	INDUSTRIAL SD CARD,16GB,-40C TO 85C
783660-01	156844A-01(Rev A or higher)	SET OF 3 SD SLOT COVERS FOR CDAQ AND CRIO
783661-10	749558-01	ENCODER CABLE, 10FT, JAE CONNECTOR (ENCODER END) TO FLYING LEADS
783668-01	749529-01	Panel Mount Kit, 12 Inch,15 Inch,17 Inch TSM
783669-01	749530-01	Rack Mount Kit, 12 Inch TSM
783670-01	749531-01	Rack Mount Kit, 15 Inch TSM
783671-01	749532-01	Rack Mount Kit, 17 Inch TSM
783672-01	749533-01	Desk Stand, 12 Inch TSM, VESA 100/75MM
783673-01	749534-01	Desk Stand for 15 Inch,17 Inch TSM,VESA 100/75MM
783674-01	749535-01	Desk Mountable ARM for 12 Inch,15 Inch,17 Inch TSM
783675-01	749536-01	Wall Mountable 0 - 90 Degree Adjustable Stand 12 Inch TSM, VESA 75/100
783702-01	154860A-N18(Rev A or higher)	NI-XNET LIN TRANSCEIVER CABLE, 18 IN.
783705-01	749599-01	AKM22C-CKB2DB00 BRUSHLESS SERVOMOTOR, OPEN KEYWAY, 24 VDC BRAKE, MULTI-TURN ABS ENDAT SINE ENCODER
783706-01	749600-01	AKM31C-CCCNC-00 BRUSHLESS SERVOMOTOR, CLOSED KEYWAY, W/O BRAKE, SMART FEEDBACK
783707-03	749601-01	CP-507CDAN-03-0 MOTOR POWER CABLE W/BRAKE LINES, FLEXING, 3M
783708-10	749602-01	CF-SB7374N-10-0 MOTOR FEEDBACK CABLE, SINE ENCODER, FLEXING, 10M
783709-03	749603-01	CF-DA0374N-03-0 MOTOR FEEDBACK CABLE, SFD, FLEXING, 3M
783745-01	749604-01	AKM42J-VBCNC-00 GEARMOTOR, 100MM FRAME, 25:1 RATIO, SFD FEEDBACK
783746-01	749605-01	AQT060-010-0-MMR-725, AQUATRUE GEARHEAD, 60MM FRAME, 10:1 RATIO
783747-01	749606-01	AKM33H-CNKNC-3K BRUSHLESS SERVO MOTOR
783751-01	749633-01	AKD-P00606-ICEC-0000, ETHERCAT SERVO DRIVE, 6A, 120/240 VAC
783752-01	749608-01	MYPARTS KIT FROM TEXAS INSTRUMENTS
783754-01	749663-01	CAMERA, BASLER ACE, ACA2000-165UC, 2048 X 1088,165 FPS, COLOR
783755-01	749664-01	CAMERA, BASLER ACE, ACA2000-165UC, 2048 X 1088,165 FPS, COLOR
783756-01	749665-01	CAMERA, BASLER ACE, ACA2040-90UM, 2048 X 2048, 90 FPS, MONOCHROME
783757-01	749666-01	CAMERA, BASLER ACE, ACA2040-90UC, 2048 X 2048, 90 FPS, COLOR
783787-01	768280-01	NI 9981, STRAIN RELIEF AND OPERATOR PROTECTION FOR 10-POS SPRING TERM (QTY 1)
783788-01	762131-01 762744-01	NI 9988D, SOLDER CUP ACCESSORY FOR NI 9218 DSUB (QTY 2)

Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxxX-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
783799-01	157824A-01(Rev A or higher)	2-POS MICRO-FIT PLUG AND CRIMP TERMINAL KIT
783804-01	762916-01	Strain Relief and Operator Protection for 6-POS Screw Term (QTY 2)
783805-01	749648-01	XT80-005-0-RM-090-40 TRUE PLANETARY GEARHEAD, SIZE 80, 5:1 RATIO, SIZE 090-1 REDIMOUNT
783807-01	749654-01	AKM22C-BNB2C-00 BRUSHLESS SERVOMOTOR, NEMA MOUNT, BRAKE, SMART FEEDBACK
783808-01	749655-01	AKM22C-BNBNC-00 BRUSHLESS SERVO, NEMA MOUNT, SMOOTH SHAFT, W/O BRAKE, SMART FEEDBACK DEVICE
783809-02	183882-02	BNC MALE (PLUG) TO BNC MALE (PLUG) 2M CABLES
783810-01	749660-01	AKM11E-BNMN2-00 BRUSHLESS SERVO, NEMA MOUNT, SMOOTH SHAFT, 0.5 M CABLES, W/O BRAKE, ENCODER
783811-01	749662-01	AKM52K-ANCNR-00 BRUSHLESS SERVO, SMOOTH SHAFT, INTERCONTEC CONNECTORS, RESOLVER
783812-01	769008-01	BNC MALE TO MICROGRABBER CABLE, 31 CM
783812-02	769008-02	BNC MALE TO MICROGRABBER CABLE, 87 CM
783813-01	698042-8192	8 GB UPGRADE/REPLACEMENT RAM FOR PXIE-8880
783825-01	749671-01	AKM33C-ANGNAB-00 PMSM MOTOR, INTERCONTEC CONNECTORS, BISS SINE ENCODER
783826-01	749674-01	N31HRFK-LNK-NS-00 HIGH TORQUE NEMA 34 STEP MOTOR, 8 LEAD CONNECTION, STRAIGHT KEYWAY
783843-01	749684-01	AKD-P300306-NBCC-I000, SERVO DRIVE, 3 A CONTINUOUS OUTPUT, 120/240 VAC 1 PHASE OR 3 PHASE INPUT, ETHERCAT OR CANOPEN
783844-05	749685-01	CP-SS-G1HE-05, MOTOR POWER CABLE, 5 METER
783845-05	749686-01	CF-SS-RHGE-05, RESOLVER FEEDBACK CABLE, 5 METER
783852-01	749690-01	AKM53Q-ANCNC-00 PMSM MOTOR, SMOOTH SHAFT, DUAL 90° INTERCONTEC CONNECTORS, SFD FEEDBACK
783853-01	749691-01	AKM62Q-ANCNC-00 PMSM MOTOR, SMOOTH SHAFT, DUAL 90° INTERCONTEC CONNECTORS, SFD FEEDBACK
783874-01	749695-01	AKM12C-ANY2C-00 AKM PMSM SMOOTH SHAFT, YTEC CONNECTOR, 24VDC BRAKE, SFD FEEDBACK, NO SHAFT SEAL
783875-06	749696-01	CM11A3-010-006-00, MOTOR CABLE, 230V, 3/6A, BRAKE, 6 METER
783876-06	749697-01	CFS0A3-002-006-00, FEEDBACK CABLE, 6 METER
783877-01	749698-01	AKM53H-ACCNC-00 PMSM MOTOR, CLOSED KEYWAY, INTERCONTEC CONNECTOR, SFD FEEDBACK
783900-01	155866B-01	NI Savage T-Bench CIB Mount For PXI
783904-01	158320A-01(Rev A or higher)	REPLACEMENT USB CABLE FOR USB-5680 POWER SENSOR
783941-01	749728-01	AKM63G-VBCNC-00 PMSM GEARMOTOR, 25:1 REDUCTION, 90° DUAL INTERCONTEC CONNECTORS, SFD FEEDBACK
783942-01	749729-01	AKD SERIES BRUSHLESS SERVO DRIVE, RATED 6 A CONTINUOUS 240/480 VAC 3 PHASE, WITH ANALOG COMMAND
783955-01	749732-01	VT006-028-0-RM060-6 VALUETRUE GEARHEAD, SIZE 006, 28:1, SIZE 060 REDIMOUNT FOR AKM2XX - AX MOTOR
783956-01	749733-01	VT006-035-0-RM060-6 VALUETRUE GEARHEAD, SIZE 006, 35:1, SIZE 060 REDIMOUNT FOR AKM2XX - AX MOTOR
783957-01	749734-01	NT60-030-0-RM060-6 NEMATRUER GEARHEAD, SIZE 23, 30:1, WITH SIZE 060 REDIMOUNT FOR AKM2XX - AX MOTOR
783960-01	749737-01	AKM12C-AKCNC-00 PMSM MOTOR, INTERCONTEC CONNECTORS, W/O BRAKE, SFD FEEDBACK
783961-01	749738-01	XT40-010-0-RM040-130 XTRUE TRUE PLANETARY GEARHEAD, SIZE 40, 10:1 RATIO, SIZE 040 REDIMOUNT
783962-01	749741-01	EC2-AKM23D-B2C-2005B-200-MF190-FT1M-C0 ELECTRIC CYLINDER
783965-01	749740-01	AKM44E-BKCNC-00 BLDC MOTOR, INTERCONTEC CONNECTORS, W/O BRAKE, SFD FEEDBACK
783972-01	749746-01	AKM32H-ANCNR-00 BLDC MOTOR, INTERCONTEC CONNECTORS, W/O BRAKE, RESOLVER FEEDBACK
783973-01	749747-01	AKM22E-CKBNC-00 PMSM MOTOR, ALT STD MOUNT, INTERCONTEC CONNECTORS, W/O BRAKE, SFD FEEDBACK
783976-01	769041-01	MINI-SAS HD X4 CABLE, 1M
783977-01	769041-03	MINI-SAS HD X4 CABLE, 3M

Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxxX-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
783982-01	768384-01	MODULE, SFP+ TRANSCEIVER, 10GB ETHERNET, 850NM MULTIMODE
783988-01	749771-01	AKM33E-CCCNC-00 BLDC MOTOR, INTERCONTEC CONNECTORS, W/O BRAKE, SFD FEEDBACK
783994-01	749773-01	AKM22E-ANB2C-0W PMSM MOTOR, INTERCONTEC CONNECTORS, 24 VDC BRAKE, SMART FEEDBACK, WASHDOWN
783995-01	749774-01	AKM32E-ANC2C-0W PMSM MOTOR, INTERCONTEC CONNECTORS, 24 VDC BRAKE, SMART FEEDBACK, WASHDOWN
783996-01	749775-01	AKM24D-ANB2C-0W PMSM MOTOR, INTERCONTEC CONNECTORS, 24 VDC BRAKE, SMART FEEDBACK, WASHDOWN
783997-01	749776-01	NTR23-010-0-RM060-6, NEMATRU 90 RIGHT ANGLE GEARHEAD, SIZE 023, 10:1 RATIO, SIZE 060 REDIMOUNT
783998-01	749777-01	NTR23-200-0-RM060-6, NEMATRU 90 RIGHT ANGLE GEARHEAD, SIZE 023, 200:1 RATIO, SIZE 060 REDIMOUNT
784000-01	158656A-01	TRIAxIAL ADAPTER FOR NI SYSTEM SMU
784076-01	763990-01	SFP+ CABLE, 1M
784076-03	763990-03	SFP+ CABLE, 3M
784076-0R5	763990-0R5	SFP+ CABLE, 0.5M
784077-01	763852-01	SFP+ 1 GBE KIT
784093-01	749840-01	AKM43E-ANC2C-00 PMSM MOTOR, INTERCONTEC CONNECTORS, 24 VDC BRAKE, SMART FEEDBACK
784098-01	749843-01	AKM65M-ACCNC-00, PMSM MOTOR, CLOSED KEYWAY, W/O SHAFT SEAL, SFD FEEDBACK
784123-01	749852-01	AKM32H-ANC2AB-00 PMSM MOTOR, 24 VDB BRAKE, BISS SINE ENCODER
784136-01	611484-01	EMI SUPPRESSION FERRITE (QTY 1)
784151-01	749853-01	CP-102AAAN-05-0 MOTOR POWER CABLE, 5.0 METER FOR S200 DRIVES
784152-01	749854-01	CF-DA0111-05-0 MOTOR FEEDBACK CABLE, 5.0 METER FOR S200 DRIVES
784153-01	749855-01	CK-S200-IP-AC-TB CONNECTOR KIT FOR S200 DRIVES, I/O AND INPUT POWER MATING CONNECTORS
784154-01	749856-01	S20260-VTS BRUSHLESS SERVO DRIVE, 120/240 VAC, 1.5 A, SFD AND HALLS SUPPORT
784159-01	749857-01	CCJ1A1-015-003-00 HYBRID GEN 3 SFD POWER/FEEDBACK CABLE, 3M
784160-01	749858-01	AKM31C-ANDNCA00 BLDC MOTOR, SINGLE INTERCONTEC, W/O BRAKE, SFD GEN3
784161-01	768390-01	EXTRA POWER CONNECTORS FOR NI 9218 LEMO (QTY 5)
784184-10	784184-10	FIBER CABLE, MULTIMODE, OM3, 10M
784195-01	750041A-01	AKM33C-ANCNC-00 PMSM MOTOR, SMOOTH SHAFT, DUAL 90° INTERCONTEC CONNECTORS, SFD FEEDBACK
784218-01	750062-01	AKM23D-CKC2DB-00 PMSM MOTOR, ALT. STD. MOUNT, DUAL INTERCONTEC, 24VDC BRAKE, ENDAT FEEDBACK
784219-01	750063-01	AKM24F-CKC2DB-00 PMSM MOTOR, ALT. STD. MOUNT, DUAL INTERCONTEC, 24VDC BRAKE, ENDAT FEEDBACK
784220-01	750064-01	AKM73P-ANCNC-00 PMSM MOTOR, 90° INTERCONTEC CONNECTORS, SFD FB
784221-01	769121-01	VF-SB4474N-12-0 MOTOR FEEDBACK CABLE, ENDAT ENCODER
784222-01	750065-01	AKM23D-ANCNC-00 PMSM MOTOR, 90° INTERCONTEC CONNECTORS, SFD FB
784230-01	750165-01	CAMERA, BASLER ACE, ACA2500-60UM, 2590 X 2048, 60 FPS, MONOCHROME
784243-01	750150-01	AKD-B02406-NBAN-0000 SERVO DRIVE, 24 A \OUTPUT, 240 VAC 3 PHASE INPUT, WITH ANALOG COMMAND
784246-01	750153-01	VTR006-010-0-RM060-6 VALUETRUE HELICAL RIGHT ANGLE GEARHEAD, SIZE 006, 10:1, 060 REDIMOUNT
784247-01	750168-01	CH054A-13-3305 CARTRIDGE DDR 480 V PMSM, ROTATABLE CONNECTORS, SOLID SHAFT, BISS ENCODER
784248-01	750154-01	AKM21E-ANBNC-00+VTR006-101 GEARMOTOR, PRECISION 10:1 RIGHT-ANGLE GEARHEAD, 90° INTERCONTEC, SFD FB
784258-01	750174-01	CAMERA, BASLER ACE, ACA3800-10GM, 3840 X 2748, 10 FPS, MONOCHROME
784259-01	750175-01	CAMERA, BASLER ACE, ACA3800-10GC, 3840 X 2748, 10 FPS, COLOR
784260-01	750176-01	CAMERA, BASLER ACE, ACA645-100UM, 658 X 492, 100 FPS, MONOCHROME
784261-01	750177-01	CAMERA, BASLER ACE, ACA645-100UC, 658 X 492, 100 FPS, COLOR
784283-01	750184-01	AKM43E-ANDNGF00 PMSM, INTL STD MOUNT, NO BRAKE, MULTI-TURN HIPERFACE FEEDBACK

Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxxX-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
784284-01	750185-01	AKD-P00306-NBCC-I000 SERVO DRIVE, 3.0 A CONT, 120/240 VAC, ETHERCAT/CANOPEN, ITALIAN DOCUMENTATION
784285-01	769129-01	AK6-GE3-D-M23-SC FEEDBACK CABLE, SFD 3RD GEN, M23 PLUG
784288-01	750186-01	VTR006-015-0-RM060-6 RIGHT ANGLE GEARHEAD, SIZE 006, 15:1, 060 REDIMOUNT FOR AKM2XX-AX MOTOR.
784306-01	140001B-04L 158299A-01 723508-01 743149-01 747647-01	CDA-2990 8 CHANNEL CLOCK DISTRIBUTION ACCESSORY WITH GPSDO
784365-01	159878B-01	NI 793R PANEL MOUNT ACCESSORY KIT
784576-01	769041-0R5	CABLE ASSEMBLY, MINISAS HD TO MINISAS HD PASSIVE COPPER, 0.5 M
784686-01	769170-01	POWER CORD, 250V, 10A, CHINA
784796-01	750509-01	PXIe AVIONICS INTERFACE MODULE FROM BALLARD, MIL-STD-1553 - 1 CHANNEL (SINGLE FUNCTION)
784797-01	750510-01	PXIe AVIONICS INTERFACE MODULE FROM BALLARD, MIL-STD-1553 - 2 CHANNEL (SINGLE FUNCTION)
784798-01	750511-01	PXIe AVIONICS INTERFACE MODULE FROM BALLARD, MIL-STD-1553 - 4 CHANNEL (SINGLE FUNCTION)
784799-01	750512-01	PXIe AVIONICS INTERFACE MODULE FROM BALLARD, MIL-STD-1553 - 1 CHANNEL (MULTI-FUNCTION)
784800-01	750513-01	PXIe AVIONICS INTERFACE MODULE FROM BALLARD, MIL-STD-1553 - 2 CHANNEL (MULTI-FUNCTION)
784801-01	750514-01	PXIe AVIONICS INTERFACE MODULE FROM BALLARD, MIL-STD-1553 - 4 CHANNEL (MULTI-FUNCTION)
784802-01	750506-01	PXIe AVIONICS INTERFACE MODULE FROM BALLARD, ARINC429 - 8 CHANNEL
784803-01	750507-01	PXIe AVIONICS INTERFACE MODULE FROM BALLARD, ARINC429 - 16 CHANNEL
784804-01	750508-01	PXIe AVIONICS INTERFACE MODULE FROM BALLARD, ARINC429 - 32 CHANNEL
785023-10	769170-01	POWER CORD FOR USRP RIO, CHINA
785024-01	142933A-01(Rev A or higher) 740732-01 740911-01 741514-01 745444-01 760832-01 764482-01 764483-01 772164-02 745047-01 747647-01 745362-01 745417-01	SCB-100A NOISE REJECTING, SHIELDED I/O CONNECTOR BLOCK
785074-01	750747-01	AKM24F-BNDNCA-00 MOTOR, SFDGEN3, NEMA MOUNT
785075-01	750748-01	AKM33H-ANDNCA-00 MOTOR, SFDGEN3
785082-01	159583A-01(Rev A or higher)	NI 9939 BACKSHELL FOR 16-POS SPRING TERMINAL CONNECTOR BLOCK (QTY 1)
785083-01	768937-01	NI 9975 16-POS SPRING TERMINAL CONNECTOR BLOCK (QTY 1)
785084-06	763187-06	CABLE ASSY,SMA-SMA,M/M,SHELL,BLUE FEP JACKET,6"
785084-08	763187-08	CABLE ASSY,SMA-SMA,M/M,SHELL,BLUE FEP JACKET,8"
785084-12	763187-12	CABLE ASSY,SMA-SMA,M/M,SHELL,BLUE FEP JACKET,12"
785084-18	763187-18	CABLE ASSY,SMA-SMA,M/M,SHELL,BLUE FEP JACKET,18"
785084-24	763187-24	CABLE ASSY,SMA-SMA,M/M,SHELL,BLUE FEP JACKET,24"
785084-28	763187-28	CABLE ASSY,SMA-SMA,M/M,SHELL,BLUE FEP JACKET,28"
785085-01	612271-01	ATTENUATOR,COAXIAL,3DB,SMA SS,DC-18GHZ,2W,50 OHM
785086-01	612272-01	ATTENUATOR,COAXIAL,5DB,SMA SS,DC-18GHZ,2W,50 OHM

Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxxX-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
785087-01	749842-01	SPLITTER MODULE, 1X4, FOR 4 CHANNEL PXIE-5668R MIMO KIT
785088-01	158813A-01(Rev A or higher) 749832-01	SPLITTER MODULE, 1X2, FOR 2 CHANNEL PXIE-5668R MIMO KIT
785089-01	155082B-01	CABLE ASSY, SMA-SMA, RF-OUT 5654 TO RF AMP-IN, PXIE-5696
785090-01	157672A-05(Rev A or higher)	CABLE, SMB-SMB, ALC IN PXIE-5654 TO ALC OUT PXIE-5696
785211-01	750889-01	AKM24D-BNG2C-00 SERIES BRUSHLESS SERVOMOTOR
785212-01	750890-01	AKM24D-BNGNC-00 BRUSHLESS SERVOMOTOR
785486-01	143340A-01 143426A-01 147052A-01 781233-02	CABLE KIT, OCULINK X4, 1M
785493-01	763830-01	MMWAVE SYSTEM - US POWER CORD (120VAC)
785550-03	143191A-03	CABLE ASSEMBLY, MXI-EXPRESS, GEN 3 X8, 3M
785599-01	143714D-01 144980A-01 146122A-01 146504A-01 720411-01	CABLE ASSEMBLY, UPS, EPO, BYO ATE RAIL KIT, MODIFIED, 19 INCH, APC SRTRK4 UPS ASSY, CABLE, GND, 10-32 RING TERMINALS, 10AWG, 1M CABLE ASSEMBLY, THERMOSTAT TO THERMOSTAT, BYO ATE THERMOSTAT, MANUAL RESET, OPEN 80C, B-203S MOUNTING HARDWARE, T-147 TERMINALS
785602-01	142071A-06(Rev A or higher)	3U MONITOR ADJUSTABLE MOUNTING ARM
785631-02	146122A-02	GROUNDING CABLE, 2M
785633-01	740400-01 743042-01 773138-01	VHDCI CONNECTOR, 68-PIN, R-ANGLE, THROUGH HOLE MOUNT
785634-01	740400-01 743042-01 771773-01	VHDCI CONNECTOR, DUAL STACK, 68-PIN, R-ANGLE, THROUGH HOLE MOUNT
785674-01	751293-01	AC POWER SUPPLY FOR RMC-8357
785675-01	751294-01	DC POWER SUPPLY FOR RMC-8357
785753-01	771492-01 743042-01 740400-01	VHDCI CONNECTOR, 68-PIN, VERTICAL, THROUGH HOLE MOUNT
785821-01	143597A-04 146878A-01 146880A-01 146881A-01	USRP E310/E312/E313 JTAG/AVR INTERFACE CABLE ACCESSORY KIT 4"
785827-01	140166A-01 143598A-04 146878A-01 146879A-01	USRP B200MINI SERIES JTAG/FX3 ARM INTERFACE CABLE ACCESSORY KIT 4"
785984-01	146989A-01	ADAPTER MOUNT FOR THE NI-9145 TO MATCH THE MOUNTING HOLES OF THE NI-9144
786139-01	754022-01	FOREIGN OBJECT KIT
786186-01	147560A-01(Rev A or higher)	RACKMOUNT KIT FOR RMX-410X 2U DC POWER SUPPLIES
786199-02	763576-02	MMPX (M) TO SMA (M) - 2 METER LENGTH SINGLE CABLE
786201-02	763576-02	MMPX (M) TO SMA (M) - 2 METER - PHASE MATCHED - DIFFERENTIAL I/Q SET (X4)
786257-01	148420A-01	COAXIAL CABLE SMB-SMB 1M RG 174 50 OHMS
786300-01	159075A-01 741208-02	1200W UPGRADE/REPLACEMENT POWER SUPPLY
786324-02	148002A-02 740972-01 741208-02 741520-01 743132-01	FAN REPLACEMENT KIT FOR PXIE-1084 CHASSIS
786335-01	143426A-01 141180A-01L	SCB-8 NOISE REJECTING, SHIELDED NANO-PITCH CONNECTOR BLOCK
786338-01	750049-01	SPARE KIT, CASTER, 3 IN, T2

Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxxX-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
786341-01	152678A-01 158940A-01	SHIELDED CABLE FOR PXIE-4330 AND PXIE-4331 TO RACKMOUNT TERMINAL BLOCK, 1 METER
786358-01	723594-01	POWER SUPPLY,S6-052A0P-USB,IN 100-240VAC 50-60HZ/OUT 5V 2KMA,UNIVERSAL INPUT W/USB
786371-01	147783A-01	18-SLOT CHASSIS FRONT RACK MOUNT KIT, EXTENDED RECESS
786372-01	147784A-01	18-SLOT CHASSIS REAR RACK MOUNT KIT, EXTENDED RECESS
786376-01	769524-01	POWER CORD, AC, JAP, 125VAC, 15A
786377-01	769525-01	POWER CORD, AC, JAP, 125VAC, 12A
786380-03	769430-01	DISPLAY PORT PANEL-MOUNT EXTENSION CABLE, 3FT
786385-01	146927A-01	UBX DAUGHTERBOARD CPLD JTAG CABLE ACCESSORY KIT 24"
786386-01	143426A-01(Rev A or higher) 146724A-0R3(Rev A or higher)	VRTS CABLE KIT, BASE CONFIGURATION, 1 OBJECT
786387-01	143045A-0R25 146700A-01 146701A-01	VRTS CABLE KIT, ADD-ON VDG, 1 PER OBJECT 2-4
786388-01	143426A-01 146724A-0R3	VRTS CABLE KIT, ADD-ON VST, 3RD OBJECT
786402-01	754002-01	DS4-100-P-5G-AKM23D-B2DA-X23-0E6-PU6E- LN1-HN1(-)-E3-P1, PRECISION TABLE
786423-01	146238A-01	CABLES FOR CONNECTION CTS II FOR EMV/NFC 9079505
786431-01	147622A-01	NI-9963, BACKSHELL FOR 28 POS SPRING TERMINAL (QTY 1)
786443-01	147831A-01	FD-11960, DIN RAIL MOUNT KIT FOR FIELDDAQ
786454-01	146502A-02 147460A-02 150732A-01	PXI 2-SLOT MECHANICAL STARTER KIT
786480-01	754028-01	TPT CONNECTION UNIT + TPT 2/MP1
786495-01	754058-01	QI COIL TPR CAL
786533-01	754267-01	RACKMOUNT KIT FOR RMX-400X DC ELECTRONIC LOADS, HOLDS ONE MAINFRAME
786651-01	146831B-01L	ISO REFERENCE PICC FOR QI TESTING (40X40, 80 LOOPS)
786668-02	148597A-02	SHDB9M-DB9F-BNCM, CURRENT TRANSDUCER SHIELDED 9-PIN D-SUB CABLE WITH BNC, 2 M
786668-03	148597A-03	SHDB9M-DB9F-BNCM, CURRENT TRANSDUCER SHIELDED 9-PIN D-SUB CABLE WITH BNC, 3 M
786668-05	148597A-05	SHDB9M-DB9F-BNCM, CURRENT TRANSDUCER SHIELDED 9-PIN D-SUB CABLE WITH BNC, 5 M
786684-04	143045A-04	VRTS CABLE - MINI-HDMI TO MINI-HDMI, 4 METERS
786685-01	100413A-01 148649A-01 741058-01	VRTS 90 DEG WR-12 WAVEGUIDE TWIST KIT
786713-01	144864A-01	COAXIAL CABLE SMB - SMA -0.5M
786714-01	144862A-01	COAXIAL CABLE BNC M / SMA M - 0.5 M
786715-01	145587A-01	COAXIAL CABLE BNC / SMB -0.5M
786716-01	144769D-01L	NFC 8 SHAPED COIL FOR CTS
786726-01	144863A-01	COAXIAL CABLE SMB F / SMA M - 0.25 M
786727-01	144865A-01	COAXIAL CABLE BNC F / SMA M - 0.5 M
786728-01	144866A-01	CABLE HE10 / HE10 - 4 CM
786729-01	144867A-01	LMA BOARD POWER SUPPLY CABLE
786730-01	144868A-01	COAXIAL CABLE BNC M / SMA M - 0.75M
786731-01	144869A-01	COAXIAL CABLE BNC M/SMB F -0.25M
786732-01	144870A-01	COAXIAL CABLE SMB F / SMB F-0.25M VERSION C
786733-01	144871A-01	COAXIAL CABLE BNC M / SMA M -0.25M
786734-01	144872A-01	POWER CABLE FOR CMR
786735-01	144893A-01	CABLE HE10-HE10 10 POINTS -0.6M
786768-01	763551-01	LOOPBACK CONNECTOR SET
786819-02	754304-01	RS-232 RJ45 TO DB9 SERIAL CABLE FOR RMX POWER SUPPLY CONTROL, 2M
786820-02	754305-01	RS-485 RJ45 TO DB9 SERIAL CABLE FOR RMX POWER SUPPLY CONTROL, 2M
786879-02	148686A-02	SHDB9M-DB9F, CURRENT TRANSDUCER SHIELDED 9-PIN D-SUB CABLE, 2 M

Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxx-X-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
786879-03	148686A-03	SHDB9M-DB9F, CURRENT TRANSDUCER SHIELDED 9-PIN D-SUB CABLE, 3 M
786879-05	148686A-05	SHDB9M-DB9F, CURRENT TRANSDUCER SHIELDED 9-PIN D-SUB CABLE, 5 M
786894-01	754431-01	FD-11954, IP67, 4 PIN M12 FEMALE (STRAIGHT) FIELD SERVICEABLE CONNECTOR, IDC
786895-01	754430-01	IP67, SHIELDED 4 PIN A-CODE M12 FEMALE (STRAIGHT) TO PIGTAIL, 1M FOR FIELDDAQ
786895-03	754430-03	IP67, SHIELDED 4 PIN A-CODE M12 FEMALE (STRAIGHT) TO PIGTAIL, 3M FOR FIELDDAQ
786895-OR3	754430-OR3	IP67, SHIELDED 4 PIN A-CODE M12 FEMALE (STRAIGHT) TO PIGTAIL, 0.3M FOR FIELDDAQ
786910-01	723633-01	POWER SUPPLY, 24 V, 2.5 A, 100-120/200-240 VAC INPUT, DIN RAIL
786911-01	754349-01	FLAT BLADE SCREWDRIVER FOR WIRELESS MONITORING DEVICES SPRING TERMINALS, 2.5 MM
786913-01	754491-01	INDUSTRIAL MICROSD CARD, 16GB, -40 TO 85C
786915-01	147221A-01	RELAY REPLACEMENT KIT,UMS05-BV51338,3W REED,QTY:10
786947-01	763187-12 763377-01 763577-OR152 786199-OR152	MMWAVE VST - IF CABLE BUNDLE FOR MFG
786969-01	130060A-01	PXIE-1092 CHASSIS FRONT RACK MOUNT KIT, EXTENDED RECESS
786970-01	130065A-01	PXIE-1092 CHASSIS REAR RACK MOUNT KIT, EXTENDED RECESS
786978-01	148572A-OR15	MINI-HDMI BREAKOUT CABLE TO 4 BNC FOR PFI 0-3, 15 CM
786979-01	148382A-OR15	MINI-HDMI BREAKOUT CABLE TO 6 BNC FOR CLK IN, CLK OUT, AND PFI 0-3, 15 CM
786989-01	754586-01	INDUSTRIAL MICROSD CARD, 32GB, -40 TO 85C
786996-01	754715-01	DENSO ROBOT 5 AXIS (ACCESSORY KIT ONLY)
786997-01	130471A-01	DENSO ROBOT 5 AXIS (ENCLOSURE ONLY)
787002-01	720411-01	SAFETY THERMOSTAT SPARE FOR ATE CORE CONFIGURATIONS
787004-01	762979-01	3-POS, SCREW TERMINAL CONNECTOR, PITCH 5.08MM (QTY 5)
787005-01	771747-01	2-POS, SPRING TERM CONNECTOR PLUG, 3.5MM PITCH (QTY 4)
787008-01	754562-01	FIELDDAQ M12 TORQUE WRENCH, USED FOR HIGH VOLTAGE I/O CONNECTION
787032-01	130331A-01 130332A-01	MICROBOT ANTENNA HOLDERS FOR NFC FORUM ANTENNAS
787037-01	148939A-01	IP67, SHIELDED 5 PIN A-CODE M12 MALE (STRAIGHT) TO BNC, 1M FOR FIELDDAQ
787037-03	148939A-03	IP67, SHIELDED 5 PIN A-CODE M12 MALE (STRAIGHT) TO BNC, 3M FOR FIELDDAQ
787037-OR3	148939A-OR3	IP67, SHIELDED 5 PIN A-CODE M12 MALE (STRAIGHT) TO BNC, 0.3M FOR FIELDDAQ
787038-01	148948A-01	IP67, SHIELDED 5 PIN A-CODE M12 MALE (RIGHT ANGLE) TO BNC, 1M FOR FIELDDAQ
787038-03	148948A-03	IP67, SHIELDED 5 PIN A-CODE M12 MALE (RIGHT ANGLE) TO BNC, 3M FOR FIELDDAQ
787045-01	765429-01	15 PIN DSUB UNSHIELDED SCREW TERMINAL BREAKOUT
787046-01	144783A-01 144784A-01 147315A-01 740004-01 740404-01 741802-01 743142-01	RACKMOUNT KIT FOR MOXA 205A-T
787051-01	130445A-01	PXI CHASSIS SIDE HANDLE AND 1-INCH RUBBER FEET KIT
787057-01	769493-01	CABLE USB TYPE C WITH RETENTION TO TYPE A 3.1 PLUG, 1M
787058-01	754602-01	BASLER ACE, ACA720-290GC, GIGE, 0.3 MP, 290 FPS, COLOR
787083-01	751824-480	DISK DRIVE,480 GB,1.8-INCH MICRO-SATA, SOLID-STATE DRIVE,MLC
787104-01	130346A-01 771931-01	NI-9962, 3-PIN 3.5MM PUSH-IN SPRING TERMINAL BLOCK PLUG, QTY 4, WITH 26 AWG FERRULES, QTY 20
787107-01	771821-01	SP18M MALE CONNECTOR WITH BACKSHELL
787108-01	130233A-01	CABLE, 3POS B2CF OMNIMATE TO PIGTAIL, AUTOMOTIVE ETHERNET, UNSHIELDED, 1M
787108-05	130233A-05	CABLE, 3POS B2CF OMNIMATE TO PIGTAIL, AUTOMOTIVE ETHERNET, UNSHIELDED, 5M
787109-15	130339A-01	CABLE, PIGTAIL TO PIGTAIL, AUTOMOTIVE ETHERNET, UNSHIELDED, 15M
787123-01	154604B-01	2-POS MICROFIT TO JACKETED PIGTAIL POWER CABLE, 1M
787136-01	131096A-01	CUSTOM, PXIE-1092 CHASSIS FRONT RACK MOUNT KIT, EXTENDED RECESS, FRONT EXTENDING

Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxxX-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
787139-01	771772-01 771785-01 771822-01 771825-01	SP8 CABLE CONNECTORS MALE AND FEMALE (WITH CONTACTS)
787140-01	771771-01 771774-01 771818-01 771821-01	SP 18 CABLE CONNECTORS MALE AND FEMALE (WITH CONTACTS)
787141-01	771818-01	SP 18 CABLE CONNECTOR FEMALE
787142-01	771822-01	SP8 CABLE CONNECTOR MALE
787143-01	771825-01	SP8 CABLE CONNECTOR FEMALE
787144-01	771771-01	SP18 CABLE CONNECTOR CONTACTS FEMALE (20)
787145-01	771774-01	SP18 CABLE CONNECTOR CONTACTS MALE (20)
787146-01	771785-01	SP8 CABLE CONNECTOR CONTACTS MALE (20)
787147-01	771772-01	SP8 CABLE CONNECTOR CONTACTS FEMALE(20)
787154-01	147202A-01	CABLE DENSO RC8 CONTROLLER TO TEST HEAD CONTROLLER
787156-01	754656-01	RMX-400X FRAME LINK CABLE
787179-01	748615-01	AXIAL FAN EBM-PAPST 252H-10,10-14VDC,ETTUS NI X3XX
787180-01	149023A-01 743598-01	USRP 2974 RACK MOUNT
787198-01	769698-01	POWER CORD, AC, IEC C19, TAIWAN (15A/250V), 2.5M
787213-01	769693-01	COMPACT SYNCHRONIZATION INTERFACE CABLE, 100MM
787214-01	147008A-01L	COMPACT SYNCHRONIZATION INTERFACE TO RTSI ADAPTER
787230-OR2	131077A-OR2	HD BNC MALE TO BNC FEMALE CABLE, 50 OHM, 20 CM
787259-01	769560-01	STORM FLEX 086, 2.92MM JACK TO SMP BULKHEAD PLUG LD , 1 METER, +/- 1.5PS
787368-01	142927B-03L	DEBUG TOOLS FOR FLEXRIO MODULE DEVELOPMENT, INTEGRATED SERIAL, EXTENDER CARD AND IO MEZZANINE
787369-01	131221A-03L	DEBUG TOOLS FOR FLEXRIO MODULE DEVELOPMENT, INTEGRATED PARALLEL, EXTENDER CARD AND IO MEZZANINE