

# Multisim CE 12.0 ADI Components

---

## Components in the Multisim Component Evaluator Analog Devices Edition by Family

	Number of Components
OPAMP	1102
ANALOG_SWITCH	178
GENERIC	130
VOLTAGE_REFERENCE	105
DIFFERENTIAL_AMPLIFIERS	103
TIL	92
INSTRUMENTATION_AMPLIFIERS	90
SPECIAL_FUNCTION	71
TRANSFORMER	32
SWITCH	30
CURRENT_SENSE_AMPLIFIERS	28
LED	23
E_SERIES_DAQ	23
BJT_NPN	22
R_SERIES_DAQ	21
LINE_RECEIVER	20
S_SERIES_DAQ	18
POWER_MOS_N	18
LINE_TRANSCEIVER	18
CONTROL_FUNCTION_BLOCKS	17
TRANSISTORS_VIRTUAL	17
RPACK	17
TRANSDUCERS	16
LINE_DRIVER	16
X_SERIES_DAQ	16
SIGNAL_VOLTAGE_SOURCES	15
AUDIO_AMPLIFIER	14
SIGNAL_CURRENT_SOURCES	14
BASIC_VIRTUAL	14
sbRIO	14
FUSE	13
SCXI	12
POWER_MOS_P	12
BJT_PNP	12
ZENER	12
PROBE	12
DARLINGTON_NPN	11

cRIO	10
MOS_ENH_P	10
CONTROLLED_VOLTAGE_SOURCES	9
IGBT	9
POWER_SOURCES	8
COMPARATOR	8
TIMER	8
SCHOTTKY_DIODE	8
MOS_ENH_N	7
WIDEBAND_AMPS	7
ADC_DAC	6
JFET_N	6
POWER_MOS_COMP	6
DIODE	5
DIGITAL_SOURCES	5
NATIONAL_INSTRUMENTS	5
MOS_DEPLETION	5
JFET_P	4
ANALOG_VIRTUAL	4
DARLINGTON_PNP	4
MIXED_VIRTUAL	3
M_SERIES_DAQ	3
BARGRAPH	3
ANALOG_DEVICES	3
NON_IDEAL_RLC	3
DIODES_VIRTUAL	2
CONTROLLED_CURRENT_SOURCES	2
SWITCHING_DIODE	2
74LS	2
POTENTIOMETER	1
VARIABLE_CAPACITOR	1
CAPACITOR	1
VIRTUAL_LAMP	1
VARIABLE_INDUCTOR	1
HEX_DISPLAY	1
CAP_ELECTROLIT	1
RESISTOR	1
INDUCTOR	1
LOSSLESS_LINE_TYPE1	1
myDAQ	1
LOSSLESS_LINE_TYPE2	1

**Components in the Multisim Component Evaluator Analog Devices Edition by Manufacturer**

Number of Components	
Analog Devices	1736
Generic	486
National Instruments	135
TI + NS Group	74
ON Semi Group	55
Zetex	15
NXP Group	14
International Rectifier	14
Intersil Group	13
Siemens	6
Grand Total	2548