



Declaration of Conformity

According to ISO/IEC 17050-1: 2010

Manufacturer Name: National Instruments Corp.
Address: 11500 North MoPac Expressway
Austin, Texas, 78759 USA
Web: www.ni.com/certification

We hereby declare under our sole responsibility that the following apparatus:

Product Description: CABLES, ACCESSORIES, & PERIPHERALS
Model Number(s): SEE LIST IN TABLE STARTING ON PAGE 2
Product Category: SEE LIST IN TABLE STARTING ON PAGE 2

Complies with the essential requirements of the following applicable European Directives:

RoHS Directive 2011/65/EU

Conformity is assessed in accordance to the following standards:

Environmental Affairs: Articles manufactured on or after the Date of Issue of this Declaration of Conformity do not contain any of the restricted substances in concentrations/applications not permitted by the RoHS Directive.

August 20, 2020, Austin, Texas USA

Date and Place of Issue

Dany Cheij, Global Product & Trade Compliance Manager



Table 1 – RoHS-Compliant Cables, Accessories, & Peripherals

Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxxX-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
192344-01	192344A-01	SHB12X-B12X, SHIELDED CABLE, LVDS, 1 METER
196284-04	196284A-04	Cable Assy IEEE 1394A to 1394B, 4 M
196304-30	196304A-30	Kit, GPS Antenna, Bullet III
196647-01	196647A-01	Cable Gland Replacement Pack, Elastomer, 4 Assorted Split and 2 Solid
196650-05	196650A-05	Ethernet Cable, Sealed Circular Plug to RJ45, 5M
197210-OR3	197210A-OR3	Mini-75 Ohm SMB Plug to Type F Female, 0.3M
197516-01	197516A-01	4x Infiniband to 4x Infiniband Cable, 1M, For NI 449x and BNC-2144
197516-02	197516A-02	4x Infiniband to 4x Infiniband Cable, 2M, For NI 449x and BNC-2144
197818-05	197818A-05	NI 17XX Pigtail Breakout Cable
198303-01	198303A-01	PC-MF4-Y Power Cable C Series Microfit Y-Adapter, Male to 2 Female, .2M
199022-02	199022A-02	10P10C-DE9M-TS SERIAL CABLE, 10-POS PLUG TO DE9-M JACKSCREWS, 2M
776784-05	182444-01 182323E-05	TYPE SH6850 68 TO 50 PIN SHIELDED CABLE,5M
776842-01	180524-10	R6850 68-50 PIN RIBBON CBL 1M
777163-01	182801A-001	MXI-2 TYPE M1,1M
777163-04	182801A-004	MXI-2 TYPE M1,4M
777166-01	182804A-001	MXI-2 TYPE M4,1M
777720-01	182444-01 185319B-01	CABLE ASSY KIT, SH5050 SHIELDED CABLE, 1 METER
777720-02	182444-01 185319B-02	CABLE ASSY KIT, SH5050 SHIELDED CABLE, 2 METER
779473-01	192516C-01	NI 9901 DESKTOP MOUNTING KIT
780151-01	765381-01	Spare Power and Motor Connectors for P7000 Stepper Drives
780553-01	765530-01 198507A-01	NI 951X Cable and Terminal Block Bundle
781384-01	747388-01	Quanser QNET MYOELECTRIC Board for NI ELVIS
781529-06	763178-01	VF-DA0474N-06 SMART FEEDBACK CABLE, AKM MOTOR TO AKD DRIVE, 6M
781723-01	151092A-01 152110A-01	NI 9925, OUTDOOR ENCLOSURE FOR NI CDAQ-9181/91
781763-01	769032-01	X16 MXI-Express Cable, 1M
781763-03	763134-03	X16 MXI-Express Cable, 3M
781822-01	152541A-01L	NI 9930Y, Motion Control Accessory, NI 9512 to Yaskawa Servo Drives
781823-01	152454A-01L	NI 9930P, Motion Control Accessory, NI 9512 to Panasonic Servo Drives
781824-01	152457A-01L	NI 9930M, Motion Control Accessory, NI 9512 to Mitsubishi Servo Drives
781965-03	748092-01	AKM211-ANMN2-02 BLDC Motor, 3270 RPM@24VDC, 0.197NM
781988-01	152829A-01(Rev A or higher)	Desktop Mounting Kit for COMPACTRIO 908X Systems
782084-01	748192-01	AKM24D-ASB2C-02 BLDC Motor, 3/8" Shaft and 1" Shaft Length
782130-001	763318-01	Motor Power Cable w/Brake, AKM Motor to AKD Drive, 1M
782130-03	763372-03	Motor Power Cable w/Brake, AKM Motor to AKD Drive, 3M
782337-06	763343-06	Flex Motor Power Cable w/Brake, AKM Motor to AKD Drive, 6M
782337-10	749249-01	CP-507CDAN-10-0, MOTOR POWER CABLE, AKM MOTOR TO AKD DRIVE, 10M
782337-20	763969-01	CP-507CDAN-20-0, MOTOR POWER CABLE, AKM MOTOR TO AKD DRIVE, 20M
782339-06	763362-06	Flex Motor Power Cable, AKM Motor to AKD Drive, 6M
782347-06	763393-06	Flex Motor Power Cable w/Brake, AKM Motor to AKD Drive, 6M
782347-20	763649-01	CP-508EDBN-20-0, FLEX MOTOR POWER CABLE WITH BRAKE, AKM MOTOR TO AKD DRIVE, 20M
782365-01	748431-01	AKM21C-CKC2C-00 PMSM Motor AC Servo with SFD Feedback, Brake
782411-01	748436-01	CS-Mount Spacer for IP Cameras
782477-01	775337-01	3 DOF Gyro Experiment, 4 Sensed add Actuated Axes, Documented System Parameters and Control VIS
782478-01	748509-01	3 DOF HELICOPTER EXPERIMENT, YAW AXIS SLIP RING, DOCUMENTED SYSTEM PARAMS AND CONTROL VIS
782479-01	775338-01	Active Suspension Experiment, Adjustable Mass & Stiffness, ABET-Aligned Lab Teaching Materials and VIS



Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxxX-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
782481-01	775335-01	4 Channel Linear Current Amplifier, 3.5A, 27V Continuous, Current Sense, Over-Heat/Current Indication
782482-01	775329-01	Ball and Beam Module, Variable Resistance POS Feedback, ABET-Aligned Lab Teaching Materials and VIS
782483-01	748513-01	COUPLED WATER TANK EXPERIMENT, 2-TANK CONFIGURATION, DOCUMENTED SYSTEM PARAMS AND CONTROL VIS
782484-01	748514-01	DOUBLE INVERTED PENDULUM MODULE FOR IP02, DOCUMENTED SYSTEM PARAMS AND CONTROL VIS
782485-01	748515-01	DOUBLE INVERTED PENDULUM MODULE FOR SRV02-ET, DOCUMENTED SYSTEM PARAMS AND CONTROL VIS
782486-01	775330-01	Rotary Flexible Link Module, Strain Gage Flex Sense, ABET-Aligned Lab Teaching Materials and VIS
782487-01	748516-01	FLEXIBLE INVERTED PENDULUM MODULE FOR IP02 BASE, DOCUMENTED SYSTEM PARAMS AND CONTROL VIS
782488-01	748517-01	GYRO / STABLE PLATFORM MODULE FOR SRV02-ET, ABET-ALIGNED LAB TEACHING MATERIALS AND VIS
782489-01	775331-01	Linear Motion Servo Plant with Inverted Pendulum Module, ABET-Aligned Lab Teaching Materials and VIS
782490-01	748518-01	LINEAR FLEXIBLE JOINT MODULE FOR THE IP02, OPT. ENCODER, ABET-ALIGNED LAB TEACHING MATERIALS AND VIS
782491-01	748519-01	LINEAR FLEXIBLE JOINT PENDULUM MODULE FOR THE IP02, ABET ALIGNED LAB TEACHING MATERIALS AND VIS
782492-01	748520-01	MAGNETIC LEVITATION EXPERIMENT, OUTPUT CURRENT SENSE, DOCUMENTED SYSTEM PARAMS AND CONTROL VIS
782493-01	775328-01	NI-M and X-Series Terminal Board for Rapid Control Prototyping, 2 AO, 8 AI, 4 ENC IN, 8 DIO
782494-01	775325-01	Q2 USB DAQ for Real-Time Controls, 2X12BIT ADC, 2X12BIT DAC, 2XENCODER IN, 2XPWM, 8 DIO
782495-01	748521-01	Q8 USB DAQ FOR REAL-TIME CONTROLS, 8X(12BIT ADC, 12BIT DAC, ENCODER IN, PWM, DI, DO), TERMINAL BOARD
782496-01	748522-01	QPID REAL-TIME MEASUREMENT AND CONTROL DAQ, 8X(16BIT ADC, 16BIT DAC, ENC IN, PWM) 56 DIO, SPI
782497-01	748523-01	QPIDE REAL-TIME MEASUREMENT AND CONTROL DAQ, 8X(16BIT ADC, 16BIT DAC, ENC IN, PWM) 56 DIO, SPI
782498-01	775332-01	Rotary Flexible Joint Module, Adjustable Spring Stiffness, ABET Aligned Lab Teaching Materials and VIS
782499-01	775333-01	Self-Erecting Rotary Inverted Pendulum Module, ABET-Aligned Lab Teaching Materials and VIS
782500-01	748524-01	SEESAW MODULE FOR IP02, HIGH RES ENC, ANTI-BACKLASH GEARS, DOCUMENTED SYSTEM PARAMS AND CONTROL VIS
782502-01	775327-01	Rotary Servo Experiment, DC Gear-Motor, Encoder, Tach, ABET-Aligned Lab Teaching Materials and VIS
782503-01	775334-01	Remote Ball Sensor Module for BB01, ABET-Aligned Lab Teaching Materials and VIS
782504-01	748529-01	Rotary Flexible Torsion Joint Module for SRV02-ET, ABET-Aligned Lab Teaching Materials and VIS
782505-01	775326-01	1 Channel Linear Voltage Amplifier, 4.16A, 24V Continuous, Current Sense, Over-Heat/Current Indication
782539-01	763357-03	CP-507CCAN-03-0 Motor Power Cable, AKM Motor to AKD Drive, 3M
782539-20	749248-01	CP-507CCAN-20-0 MOTOR POWER CABLE, AKM MOTOR TO AKD DRIVE, 20M
782539-30	749672-01	CP-507CCAN-30-0 MOTOR POWER CABLE, AKM MOTOR TO AKD DRIVE, 30M
782540-01	763560-03	CF-CB7374N-03-0 Motor Feedback Cable, AKM Motor to AKD Drive, 3M
782557-01	748581-01	ICD05-075A1P3 DDL ICD Ironcore Motor, Flying Leads (100MM) with Connector
782558-01	748582-01	ICD05-075A5P3 DDL ICD Ironcore Motor, Flying Leads (100MM) with Connector
782559-01	763582-03	M1C-03, High Flex Motor Cable, 18 AWG for 3A and 6A Drives, 3M
782560-01	763583-03	H1C-03, High Flex Hall Effect Cable, 3M
782562-01	748584-01	S77202-NANANA, Brushless Servo Drive, 72A Continuous Current, 480V



Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxxX-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
782564-01	763585-05	DE-201589, 48 AMP S700 Power Cable, 5M
782565-01	763586-05	DE-84972, Resolver Feedback Cable, 5M
782575-01	748593-01	XT060-005-0-RM-60-1 XTRUE True Planetary Gearhead, Size 60, 5:1 Ratio, Size 060-1
782599-01	748600-01	VT018-010-0-RM180-114 Valuetrue Planetary Gearhead, Size 018, 10:1 Ratio, Size 180 Redimount
782601-01	763620-01	Motor Power Cable, AKM Motor to AKD Drive, 6M, VP-508DEAN-06
782624-01	748620-01	UT014-005-0-RM142-92, Ultratrue True Planetary Gearhead, Size 014, 5:1 Ratio, Size 142 Redimount
782675-01	748650-01	K34H-RLL-LNK-NS-00 Step Motor, 4 Lead Series Connector, No Rear Shaft Ext., Straight Keyway, No Feedback
782680-01	763631-01	VP-508CEAN-01, 12 AMP AKD Power Cable, 1M
782680-03	763640-01	VP-508CEAN-03, 12 AMP AKD Power Cable, 3M
782680-06	763642-01	VP-508CEAN-06, 12 AMP AKD Power Cable, 6M
782680-09	763643-01	VP-508CEAN-09, 12 AMP AKD Power Cable, 9M
782680-12	763644-01	VP-508CEAN-12, 12 AMP AKD Power Cable, 12M
782682-09	763645-01	VP-508CFAN-09, 12 AMP AKD Power/Brake Cable, 9M
782683-01	763646-01	VP-508DEAN-01, 20 AMP AKD Power Cable, 1M
782683-03	763653-01	VP-508DEAN-03, 20 AMP AKD Power Cable, 3M
782683-09	763655-01	VP-508DEAN-09, 20 AMP AKD Power Cable, 9M
782683-12	763658-01	VP-508DEAN-12, 20 AMP AKD Power Cable, 12M
782684-01	763659-01	VP-508DFAN-01, 20 AMP AKD Power/Brake Cable, 1M
782684-03	763660-01	VP-508DFAN-03, 20 AMP AKD Power/Brake Cable, 3M
782684-06	763661-01	VP-508DFAN-06, 20 AMP AKD Power/Brake Cable, 6M
782684-09	763666-01	VP-508DFAN-09, 20 AMP AKD Power/Brake Cable, 9M
782684-12	763667-01	VP-508DFAN-12, 20 AMP AKD Power/Brake Cable, 12M
782687-09	763668-01	VF-DA0474N-09, Smart Feedback (SFD) Cable, 9M
782689-01	748645-01	Q1-CRIO, Data Acquisition and Control Module for COMPACTRIO, 1 AO, 1 AI, 2 ENCODER IN
782712-01	748676-01	NTR23-500-0-RM060-311, NEMATTRUE 90 Right Angle GEARHEAD, Size 023, 500:1 Ratio, Size 060 Redimount
782786-01	697211-02	16GB INDUSTRIALLY RATED COMPACT FLASH CARD FOR TPC-22XX
782848-01	748752-01	Replacement System Monitor Assembly For NI PXI-1016 Chassis
782854-01	153700A-01(Rev A or higher)	NI HDD-8266 24-DRIVE, 24TB SATA, CABLED PCIE HDD ENCLOSURE W/RAID
782858-01	153700A-02	NI HDD-8266 24-DRIVE, 3.5TB SAS, CABLED PCIE HDD ENCLOSURE W/RAID
782876-01	748754-01	KBM-57S01-A00 Frameless Brushless Servomotor, Stack Length 01, A Winding
782933-12	763839-12	CF-SS-CHUE-12 COMMUTATING ENCODER FEEDBACK CABLE, AKM MOTOR TO AKD DRIVE, 12M
782964-20	749250-01	CF-DA0374N-20-0, MOTOR FEEDBACK CABLE, AKM MOTOR TO AKD DRIVE, 20M
783077-01	748884-01	3YLN-06 MOTOR CABLE CHOKE, 6 AMP CONTINUOUS OR LESS
783079-01	748885-01	XT120-020-0-RM115-71 XTRUE TRUE PLANETARY GEARHEAD, SIZE 120, 20:1 RATIO, SIZE 115 REDIMOUNT
783085-01	748887-01	P70530-PNN DRIVE, 20-75 VDC, 5 AMP CONT, MOTION NODE INDEXING, NO FEEDBACK DEVICE SUPPORT
783099-01	749158-01	SISU 1004 4-AXIS STEPPER MOTOR INTERFACE MODULE FOR CRIO
783137-01	749084-01	VLM32H-CLNC-00, BRUSHLESS SERVO, METRIC MOUNT, SMOOTH SHAFT, FLYING LEAD CABLES, SMART FEEDBACK, 1 M LEADS
783158-01	763946-01	CP-508DCAN-06-0, FLEX MOTOR POWER CABLE W/BRAKE, AKM MOTOR TO AKD DRIVE, 6M
783159-01	763947-01	CF-SB7374N-06-0, FLEX MOTOR FEEDBACK CABLE, AKM MOTOR TO AKD DRIVE, 6M
783159-30	749673-01	CF-SB7374N-30-0, FLEX MOTOR FEEDBACK CABLE, AKM MOTOR TO AKD DRIVE, 30M
783166-01	749159-01	SISU RJ45 TO TERMINALS BREAKOUT FOR THE SISU-1004 C SERIES MODULE
783171-01	749114-01	KOLLMORGEN KCM-E200 CAPACITOR MODULE
783172-01	749115-01	KOLLMORGEN KCM-E400 CAPACITOR MODULE
783190-01	749130-01	XT80-030-0-RM090-6, XTRUE GEARHEAD, SIZE 80, 30:1 RATIO, 090 REDIMOUNT
783197-01	749138-01	XT60-020-0-RM060-6, XTRUE GEARHEAD, SIZE 60, 20:1 RATIO, 060 REDIMOUNT
783204-01	763978-01	CF-RA2574N-20-0 MOTOR FEEDBACK CABLE, AKM MOTOR TO AKD DRIVE, 20M



Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxxX-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
783312-01	749194-01	VLM22C-DKNC-00 BRUSHLESS SERVO, NEMA 23 MOUNT, 1/4" SMOOTH SHAFT, SMART FEEDBACK, 1 M LEADS
783319-01	763200-01	ENCODER FEEDBACK CABLE, CF-SB7374N-20, AKM MOTOR TO AKD DRIVE, 20 M
783321-01	749212-01	FILTER, DE-201569, 3NF-07
783322-01	749213-01	FILTER, DE-201570 3NF-16
783323-01	749214-01	FILTER, DE-201571 3NF-30
783324-01	749209-01	SERVO DRIVE EXTERNAL RESISTOR, BAR-500-33, 500 W, 33 OHMS
783325-01	749210-01	SERVO DRIVE EXTERNAL RESISTOR, BAS-4000-23, 4000 W, 23 OHMS
783326-01	749211-01	SERVO DRIVE EXTERNAL RESISTOR, BAR-1500-33, 1500 W, 33 OHMS
783384-01	749254-01	NTR34-006-0-RM090-40, NEMATRU 90 RIGHT ANGLE GEARHEAD, SIZE 34, 6:1 RATIO, SIZE 090 REDIMOUNT
783386-01	749276-01	KBMS-17H02-A00 SERVOMOTOR, HIGH VOLTAGE INSULATION, STACK LENGTH 02, A WINDING
783387-01	749277-01	KBMS-17H02-D00 SERVOMOTOR, HIGH VOLTAGE INSULATION, STACK LENGTH 02, D WINDING
783388-01	749278-01	KBMS-17H03-A00 SERVOMOTOR, HIGH VOLTAGE INSULATION, STACK LENGTH 03, A WINDING
783389-01	749279-01	KBMS-25H03-D00 SERVOMOTOR, HIGH VOLTAGE INSULATION, STACK LENGTH 03, D WINDING
783390-01	749280-01	S20330-VTS SERVO DRIVE, 90 VDC, 3 AMP CONTINUOUS, SMART FEEDBACK DEVICE AND HALLS SUPPORT
783391-01	749281-01	S20630-VTS SERVO DRIVE, 90 VDC, 6 AMP CONTINUOUS, SMART FEEDBACK DEVICE AND HALLS SUPPORT
783438-01	763112-01	CF-SB7374N-03-0 MOTOR FEEDBACK CABLE, ENDAT ENCODER, FLEXING, 3M
783439-01	749321-01	D083M-22-1310 HOUSED DDR 230V BRUSHLESS SERVOMOTOR, SINGLE TURN ABSOLUTE SINE ENCODER (2048 LINE)
783569-01	156783A-01(Rev A or higher)	VIRTUALBENCH DESKTOP MOUNTING KIT
783606-01	749491-01	D063M-12-1310 HOUSED DDR SERIES 230V BRUSHLESS SERVOMOTOR, ABSOLUTE SINE ENCODER (2048 LINE)
783707-03	749601-01	CP-507CDAN-03-0 MOTOR POWER CABLE W/BRAKE LINES, FLEXING, 3M
783708-10	749602-01	CF-SB7374N-10-0 MOTOR FEEDBACK CABLE, SINE ENCODER, FLEXING, 10M
783709-03	749603-01	CF-DA0374N-03-0 MOTOR FEEDBACK CABLE, SFD, FLEXING, 3M
783746-01	749605-01	AQT060-010-0-MMR-725, AQUATRU 60MM FRAME, 10:1 RATIO
783747-01	749606-01	AKM33H-CNKNC-3K BRUSHLESS SERVO MOTOR
783805-01	749648-01	XT80-005-0-RM-090-40 TRUE PLANETARY GEARHEAD, SIZE 80, 5:1 RATIO, SIZE 090-1 REDIMOUNT
783826-01	749674-01	N31HRFK-LNK-NS-00 HIGH TORQUE NEMA 34 STEP MOTOR, 8 LEAD CONNECTION, STRAIGHT KEYWAY
783844-05	749685-01	CP-SS-G1HE-05, MOTOR POWER CABLE, 5 METER
783845-05	749686-01	CF-SS-RHGE-05, RESOLVER FEEDBACK CABLE, 5 METER
783875-06	749696-01	CM11A3-010-006-00, MOTOR CABLE, 230V, 3/6A, BRAKE, 6 METER
783876-06	749697-01	CFS0A3-002-006-00, FEEDBACK CABLE, 6 METER
783900-01	155866B-01	NI Savage T-Bench CIB Mount For PXI
783904-01	158320A-01(Rev A or higher)	REPLACEMENT USB CABLE FOR USB-5680 POWER SENSOR
783955-01	749732-01	VT006-028-0-RM060-6 VALUETRU 28:1 GEARHEAD, SIZE 006, 28:1, SIZE 060 REDIMOUNT FOR AKM2XX - AX MOTOR
783956-01	749733-01	VT006-035-0-RM060-6 VALUETRU 35:1 GEARHEAD, SIZE 006, 35:1, SIZE 060 REDIMOUNT FOR AKM2XX - AX MOTOR
783961-01	749738-01	XT40-010-0-RM040-130 XTRUE TRUE PLANETARY GEARHEAD, SIZE 40, 10:1 RATIO, SIZE 040 REDIMOUNT
783997-01	749776-01	NTR23-010-0-RM060-6, NEMATRU 90 RIGHT ANGLE GEARHEAD, SIZE 023, 10:1 RATIO, SIZE 060 REDIMOUNT
783998-01	749777-01	NTR23-200-0-RM060-6, NEMATRU 90 RIGHT ANGLE GEARHEAD, SIZE 023, 200:1 RATIO, SIZE 060 REDIMOUNT
784151-01	749853-01	CP-102AAAN-05-0 MOTOR POWER CABLE, 5.0 METER FOR S200 DRIVES
784152-01	749854-01	CF-DA0111-05-0 MOTOR FEEDBACK CABLE, 5.0 METER FOR S200 DRIVES



Kit Part Number	Component/Assy. Part Number(s)	Description
e.g., 1xxxxx-xx	e.g., 1xxxxxX-xx (rev. X or higher)	Description of RoHS-compliant product (shipping kit)
784153-01	749855-01	CK-S200-IP-AC-TB CONNECTOR KIT FOR S200 DRIVES, I/O AND INPUT POWER MATING CONNECTORS
784154-01	749856-01	S20260-VTS BRUSHLESS SERVO DRIVE, 120/240 VAC, 1.5 A, SFD AND HALLS SUPPORT
784159-01	749857-01	CCJ1A1-015-003-00 HYBRID GEN 3 SFD POWER/FEEDBACK CABLE, 3M
784221-01	769121-01	VF-SB4474N-12-0 MOTOR FEEDBACK CABLE, ENDAT ENCODER
784246-01	750153-01	VTR006-010-0-RM060-6 VALUETRUE HELICAL RIGHT ANGLE GEARHEAD, SIZE 006, 10:1, 060 REDIMOUNT
784247-01	750168-01	CH054A-13-3305 CARTRIDGE DDR 480 V PMSM, ROTATABLE CONNECTORS, SOLID SHAFT, BISS ENCODER
784285-01	769129-01	AK6-GE3-D-M23-SC FEEDBACK CABLE, SFD 3RD GEN, M23 PLUG
784288-01	750186-01	VTR006-015-0-RM060-6 RIGHT ANGLE GEARHEAD, SIZE 006, 15:1, 060 REDIMOUNT FOR AKM2XX-AX MOTOR.
786402-01	754002-01	DS4-100-P-5G-AKM23D-B2DA-X23-0E6-PU6E- LN1-HN1-()-E3-P1, PRECISION TABLE
786480-01	754028-01	TPT CONNECTION UNIT + TPT 2/MP1