



DEMKO CERTIFICATE

Certificate No.	D-09301-M3
Page	1/4
Date of Issue	2024-05-13
Certificate Holder	NATIONAL INSTRUMENTS CORP 11500 N MOPAC EXPY AUSTIN, TX 78759-3504 UNITED STATES
Production site	NI HUNGARY KFT HATAR UT 1/A DEBRECEN 4031 HUNGARY
Certified Product	Measuring and Testing Equipment
Model	cDAQ-9137, cRIO-9065, cRIO-9042, cRIO-9023, cRIO-9047 See page 2 for additional Information
Trademark	 NATIONAL INSTRUMENTS ™ OR  OR NI
Ratings	N/A (Devices do not connect to Mains) Class I (PE connected), IP20, IP40 and IP30 only, see Test Report for details.
Tested according to	EN 61010-1:2010, EN 61010-1:2010/A1:2019
Test Report No.	E183728-D1012-4/A3/C0-Informative issued on 2024-05-09
Additional	This certificate is replacing the certificate No. D-09301-M2 dated 2024-02-22 due to Technical Modifications to update the Critical Components List.
Expire date	2032-06-07



Certification Manager
Thomas Wilson

This is to certify that representative sample(s) of the Product described herein ("Certified Product") have been investigated and found in compliance with the Standard(s) indicated on this Certificate, in accordance with the D-Mark Requirements. As specified in the respective appendix below the Designated Certificate holder is entitled to use the D-Mark, or its alternative for cables, for the Certified Product manufactured at the production site(s) identified above, in accordance with the D-Mark Service Agreement, including without limitation the D-Mark Testing and Certification Services Service Terms. Only those Products bearing the D-Mark should be considered as being covered by UL's D-Mark Service. This Certificate shall remain valid through the expiration date, unless terminated earlier in accordance with the Service Agreement including without limitation if the Standard identified on this Certificate is amended or withdrawn prior the expiration date.

Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65,
info.dk@ul.com
www.UL.com



Appendix DEMKO CERTIFICATE

Certificate No. D-09301-M3

Page 2/4

Date of Issue 2024-05-13

Additional Model(s):

cRIO-9022, cRIO-9023, cRIO-9024, cRIO-9025, cRIO-9030, cRIO-9031, cRIO-9032, cRIO-9033, cRIO-9034, cRIO-9035, cRIO-9036, cRIO-9037, cRIO-9038, cRIO-9039, cRIO-9040, cRIO-9041, cRIO-9042, cRIO-9043, cRIO-9045, cRIO-9046, cRIO-9047, cRIO-9048, cRIO-9049, cRIO-9053, cRIO-9054, cRIO-9055, cRIO-9056, cRIO-9057, cRIO-9058, cRIO-9063, cRIO-9064, cRIO-9065, cRIO-9066, cRIO-9067, cRIO-9068, cRIO-9074, cRIO-9075, cRIO-9076, cRIO-9081, cRIO-9082, cRIO-9111, cRIO-9112, cRIO-9113, cRIO-9114, cRIO-9116, cRIO-9118, cDAQ-9132, cDAQ-9133, cDAQ-9134, cDAQ-9135, cDAQ-9136, cDAQ-9137, NI 9145, cRIO-9146, NI 9147, cRIO-9148, NI 9149, cRIO-9154, cRIO-9155, cRIO-9157, cRIO-9159, cDAQ-9171, cDAQ-9174, cDAQ-9178, cDAQ-9179, cDAQ-9181, cDAQ-9184, cDAQ-9185, cDAQ-9188, cDAQ-9188XT, cDAQ-9189, TRC-8542, TRC-8543, TRC-8546

Products may also be referred to as NI XXXX, cRIO-XXXX, cDAQ-XXXX or XXXX, where XXXX is a four digit numbers above. Models cRIO-904x may be followed by TPM which does not affect safety.

Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65, info.dk@ul.com
www.UL.com



Appendix DEMKO CERTIFICATE


Certificate No. D-09301-M3

Page 3/4

Date of Issue 2024-05-13

Certification Mark D-Mark

The D-Mark, as displayed below, shall appear on certified products only. Except as specified below the Mark shall be legible and no Minimum size is specified.



The size of the Mark may be reduced or enlarged on the condition that it remains readable and that the proportions of width and height are kept. The use of dark text for the D-Mark on light backgrounds and light text on dark backgrounds is permitted.

The D-Mark may appear on a label, nameplate, or may be cast, stamped or molded into the product. When appearing on a label or nameplate, the Manufacturer's name or trademark along with a model number are also required on that same label or nameplate. If cast, stamped or molded, the Certificate Manufacturer's name or trademark and model number shall also appear elsewhere on the product

When putting the product on the EU market, the manufacturer's name, trademark or mark of origin must be affixed in a clearly visible location and position on the product, on the package and in the user manual. It can be affixed by label, be directly imprinted, or cast or molded into the product.

Where the size of the product does not allow the Mark, the manufacturer's name, trademark, mark of origin and model number to be legible, and appearance on a label is not desired, it is allowed to cast, stamp or mold the Mark into the product, in a size which is not visible to the naked eye, provided the legible Mark, the manufacturer's name, trademark or mark of origin and model number appears on the package and in the user manual

Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65, info.dk@ul.com
www.UL.com



Appendix DEMKO CERTIFICATE

Certificate No. D-09301-M3

Page 4/4

Date of Issue 2024-05-13

Alternate certification Mark for cables

As an alternative to the D-Mark specified above the alternate D-Mark, displayed below, can appear on certified cables only. Minimum size is not specified, as long as the mark is legible.

<DEMKO>

The alternate D-Mark may be cast, stamped or molded into the cable and continue throughout the length of the cable as specified in the applicable cable standard.

All content shall be in accordance with the details provided on this D-Mark Certificate.

Certification Body

UL International Demko A/S, Borupvang 5A, DK-2750
Ballerup, Denmark, Tel. +45 44 85 65 65, info.dk@ul.com
www.UL.com

