

Multisim 14.1 Base Edition Components

0 Ohm [CAT10-000J4LF]	0 Ohm [CR0805-J/-000ELF]	1 kOhm [4114R-2-102]	1 kOhm [4306M-102-102]
0 Ohm [CAT16-000J2GLF]	0 Ohm [CR0805-J/-000GLF]	1 kOhm [4114R-2-102LF]	1 kOhm [4306M-102-102LF]
0 Ohm [CAT16-000J2LF]	0 Ohm [CR1206-J/-000ELF]	1 kOhm [4116R-1-102]	1 kOhm [4306R-101-102]
0 Ohm [CAT16-000J4GLF]	0 Ohm [CR1206-J/-000GLF]	1 kOhm [4116R-1-102LF]	1 kOhm [4306R-101-102LF]
0 Ohm [CAT16-000J4LF]	0 Ohm [CR2010-J/-000ELF]	1 kOhm [4116R-2-102]	1 kOhm [4306R-102-102]
0 Ohm [CAT16-000J8LF]	0 Ohm [CR2512-J/-000ELF]	1 kOhm [4116R-2-102LF]	1 kOhm [4306R-102-102LF]
0 Ohm [CAY10-000J2LF]	0 Ohm [PWR6327WR000JE]	1 kOhm [4304M-101-102]	1 kOhm [4308H-101-102]
0 Ohm [CAY10-000J4LF]	0.5_AMP	1 kOhm [4304M-101-102LF]	1 kOhm [4308H-101-102LF]
0 Ohm [CAY16-000J2LF]	02BZ2.2	1 kOhm [4304M-102-102]	1 kOhm [4308H-102-102]
	02DZ4.7		
0 Ohm [CAY16-000J4LF]	05AZ2.2	1 kOhm [4304M-102-102LF]	1 kOhm [4308H-102-102LF]
0 Ohm [CAY16-000J8LF]	1 kOhm [4108R-1-102LF]	1 kOhm [4306H-101-102]	1 kOhm [4308M-101-102]
0 Ohm [CR0201-J/-000GLF]	1 kOhm [4108R-2-102]	1 kOhm [4306H-101-102LF]	1 kOhm [4308M-101-102LF]
0 Ohm [CR0402-J/-000GLF]	1 kOhm [4108R-2-102LF]	1 kOhm [4306H-102-102]	1 kOhm [4308M-102-102]
0 Ohm [CR0603-J/-000ELF]	1 kOhm [4114R-1-102]	1 kOhm [4306M-101-102]	1 kOhm [4308M-102-102LF]
0 Ohm [CR0603-J/-000GLF]	1 kOhm [4114R-1-102LF]	1 kOhm [4306M-101-102LF]	1 kOhm [4308R-101-102]

Multisim 14.1 Base Edition Components

1 kOhm [4308R-101-102LF]	1 kOhm [4310R-102-102]	1 kOhm [4420P-T01-102]	1 kOhm [4606X-AP1-102LF]
1 kOhm [4308R-102-102]	1 kOhm [4310R-102-102LF]	1 kOhm [4420P-T02-102]	1 kOhm [4606X-AP2-102LF]
1 kOhm [4308R-102-102LF]	1 kOhm [4311R-101-102]	1 kOhm [4420P-T02-102LF]	1 kOhm [4607X-101-102LF]
1 kOhm [4309R-101-102]	1 kOhm [4311R-101-102LF]	1 kOhm [4604H-101-102LF]	1 kOhm [4608H-101-102LF]
1 kOhm [4309R-101-102LF]	1 kOhm [4416P-1-102]	1 kOhm [4604X-101-102LF]	1 kOhm [4608H-102-102LF]
1 kOhm [4310H-101-102]	1 kOhm [4416P-1-102LF]	1 kOhm [4604X-102-102LF]	1 kOhm [4608M-101-102LF]
1 kOhm [4310H-101-102LF]	1 kOhm [4416P-2-102]	1 kOhm [4605M-101-102LF]	1 kOhm [4608M-102-102LF]
1 kOhm [4310H-102-102]	1 kOhm [4416P-2-102LF]	1 kOhm [4605X-101-102LF]	1 kOhm [4608X-101-102LF]
1 kOhm [4310H-102-102LF]	1 kOhm [4416P-T01-102]	1 kOhm [4605X-AP1-102LF]	1 kOhm [4608X-102-102LF]
1 kOhm [4310M-101-102]	1 kOhm [4416P-T01-102LF]	1 kOhm [4606H-101-102LF]	1 kOhm [4608X-AP1-102LF]
1 kOhm [4310M-101-102LF]	1 kOhm [4416P-T02-102]	1 kOhm [4606H-102-102LF]	1 kOhm [4608X-AP2-102LF]
1 kOhm [4310M-102-102]	1 kOhm [4416P-T02-102LF]	1 kOhm [4606M-101-102LF]	1 kOhm [4609H-101-102LF]
1 kOhm [4310M-102-102LF]	1 kOhm [4420P-1-102]	1 kOhm [4606M-102-102LF]	1 kOhm [4609M-101-102LF]
1 kOhm [4310R-101-102]	1 kOhm [4420P-2-102]	1 kOhm [4606X-101-102LF]	1 kOhm [4609X-101-102LF]
1 kOhm [4310R-101-102LF]	1 kOhm [4420P-2-102LF]	1 kOhm [4606X-102-102LF]	1 kOhm [4609X-AP1-102LF]

Multisim 14.1 Base Edition Components

1 kOhm [4610H-101-102LF]	1 kOhm [4814P-1-102LF]	1 kOhm [4816P-T01-102LF]	1 kOhm [CAT10-102J4LF]
1 kOhm [4610H-102-102LF]	1 kOhm [4814P-2-102]	1 kOhm [4816P-T02-102]	1 kOhm [CAT16-1001F4LF]
1 kOhm [4610M-101-102LF]	1 kOhm [4814P-2-102LF]	1 kOhm [4816P-T02-102LF]	1 kOhm [CAT16-1001F8LF]
1 kOhm [4610M-102-102LF]	1 kOhm [4814P-T01-102]	1 kOhm [4818P-1-102]	1 kOhm [CAT16-102J2LF]
1 kOhm [4610X-101-102LF]	1 kOhm [4814P-T01-102LF]	1 kOhm [4818P-2-102]	1 kOhm [CAT16-102J4GLF]
1 kOhm [4610X-102-102LF]	1 kOhm [4814P-T02-102]	1 kOhm [4818P-T01-102]	1 kOhm [CAT16-102J4LF]
1 kOhm [4610X-AP1-102LF]	1 kOhm [4814P-T02-102LF]	1 kOhm [4818P-T02-102]	1 kOhm [CAT16-102J8LF]
1 kOhm [4610X-AP2-102LF]	1 kOhm [4816P-1-102]	1 kOhm [4820P-1-102]	1 kOhm [CAT25-102JALF]
1 kOhm [4611M-101-102LF]	1 kOhm [4816P-1-102F]	1 kOhm [4820P-1-102LF]	1 kOhm [CAY10-102J4LF]
1 kOhm [4611X-101-102LF]	1 kOhm [4816P-1-102LF]	1 kOhm [4820P-2-102]	1 kOhm [CAY16-1001F4LF]
1 kOhm [4612X-101-102LF]	1 kOhm [4816P-2-102]	1 kOhm [4820P-2-102LF]	1 kOhm [CAY16-102J2LF]
1 kOhm [4612X-102-102LF]	1 kOhm [4816P-2-102F]	1 kOhm [4820P-T01-102]	1 kOhm [CAY16-102J4GLF]
1 kOhm [4613X-101-102LF]	1 kOhm [4816P-2-102LF]	1 kOhm [4820P-T01-102LF]	1 kOhm [CAY16-102J4LF]
1 kOhm [4614X-102-102LF]	1 kOhm [4816P-4-102]	1 kOhm [4820P-T02-102]	1 kOhm [CAY16-102J8LF]
1 kOhm [4814P-1-102]	1 kOhm [4816P-T01-102]	1 kOhm [4820P-T02-102LF]	1 kOhm [CAY17-102JALF]

Multisim 14.1 Base Edition Components

1 kOhm [CR0201-FW-1001GLF]	1 kOhm [CR1206-JW-102GLF]	1 kOhm [CRS2512-FX-1001ELF]	1 kOhm [CRT0805-FV-1001ELF]
1 kOhm [CR0201-JW-102GLF]	1 kOhm [CR2010-JW-102ELF]	1 kOhm [CRS2512-JX-102ELF]	1 kOhm [CRT1206-AV-1001ELF]
1 kOhm [CR0402-FX-1001GLF]	1 kOhm [CR2512-FX-1001ELF]	1 kOhm [CRT0402-BY-1001GLF]	1 kOhm [CRT1206-BW-1001ELF]
1 kOhm [CR0402-JW-102GLF]	1 kOhm [CR2512-JW-102ELF]	1 kOhm [CRT0402-DY-1001GLF]	1 kOhm [CRT1206-BY-1001ELF]
1 kOhm [CR0603-FX-1001ELF]	1 kOhm [CRM1206-FX-1001ELF]	1 kOhm [CRT0402-FZ-1001GLF]	1 kOhm [CRT1206-FZ-1001ELF]
1 kOhm [CR0603-FX-1001GLF]	1 kOhm [CRM1206-JW-102ELF]	1 kOhm [CRT0603-BY-1001EAS]	1 kOhm [PWR163S-25-1001F]
1 kOhm [CR0603-FX-1001HLF]	1 kOhm [CRM2010-FX-1001ELF]	1 kOhm [CRT0603-BY-1001ELF]	1 kOhm [PWR163S-25-1001J]
1 kOhm [CR0603-JW-102ELF]	1 kOhm [CRM2512-FX-1001ELF]	1 kOhm [CRT0603-DZ-1001ELF]	1 kOhm [PWR2010W1001FE]
1 kOhm [CR0603-JW-102GLF]	1 kOhm [CRM2512-FX-1001ELF]	1 kOhm [CRT0603-FY-1001ELF]	1 kOhm [PWR220T-20-1001F]
1 kOhm [CR0805-FX-1001ELF]	1 kOhm [CRM2512-JW-102ELF]	1 kOhm [CRT0603-PW-1001ELF]	1 kOhm [PWR220T-20-1001J]
1 kOhm [CR0805-JW-102ELF]	1 kOhm [CRS0805-FX-1001ELF]	1 kOhm [CRT0805-BV-1001ELF]	1 kOhm [PWR220T-35-1001F]
1 kOhm [CR0805-JW-102GLF]	1 kOhm [CRS0805-JX-102ELF]	1 kOhm [CRT0805-BW-1001ELF]	1 kOhm [PWR220T-35-1001J]
1 kOhm [CR1206-FX-1001ELF]	1 kOhm [CRS1206-FX-1001ELF]	1 kOhm [CRT0805-BY-1001ELF]	1 kOhm [PWR221T-30-1001F]
1 kOhm [CR1206-FX-1001GLF]	1 kOhm [CRS2010-FX-1001ELF]	1 kOhm [CRT0805-DV-1001ELF]	
1 kOhm [CR1206-JW-102ELF]		1 kOhm [CRT0805-DY-1001ELF]	

Multisim 14.1 Base Edition Components

1 kOhm [PWR221T-50-1001J]	1 kOhm [PWR6327W1001JE]	1 mF [T510E108M004AT E010]	1 mF [T520X108M2R5AT E010]
1 kOhm [PWR2615W1001F]	1 kOhm [WS2M1001J]	1 mF [T510E108M004AT E018]	1 mF [T520Y108M2R5AT E010]
1 kOhm [PWR263S-20-1001F]	1 kOhm [WS5M1001J]	1 mF [T510X108M004AT E018]	1 mF [T520Y108M2R5AT E015]
1 kOhm [PWR263S-20-1001FE]	1 mF [2R5TPE1000MF]		
1 kOhm [PWR263S-20-1001J]	1 mF [2SEPC1000MX]	1 mF [T510X108M004AT E023]	1 mF [T520Y108M2R5AT E025]
1 kOhm [PWR263S-35-1001F]	1 mF [ETPF1000M5H]	1 mF [T513E108M004AH 6110]	1 mF [T530X108M003AT E010]
1 kOhm [PWR263S-35-1001FE]	1 mF [ETPF1000M6H]	1 mF [T513X108M004AH 6110]	1 mF [T530X108M004AT E006]
1 kOhm [PWR263S-35-1001J]	1 mF [T491E108M004AT]		
1 kOhm [PWR4318W1001FE]	1 mF [T491X108M004AT]	1 mF [T513X108M004AH 6120]	1 mF [T530X108M2R5AT E005]
1 kOhm [PWR4318W1001JE]	1 mF [T494E108M004AT]	1 mF [T520D108M2R5AT E015]	1 mF [T530X108M2R5AT E006]
1 kOhm [PWR4525W1001J]	1 mF [T495E108M004AT E035]	1 mF [T520D108M2R5AT E030]	1 mF [T530Y108M2R5AT E005]
1 kOhm [PWR4525W1001JE]	1 mF [T495E108M006AT E050]	1 mF [T520X108M003AT E015]	1 mF [TAJD108K004RNJ]
1 kOhm [PWR6327W1001J]	1 mF [T495X108M004AT E070]	1 mF [T520X108M003AT E030]	1 mF [TAJE108K002RNJ]
			1 mF [TAJE108K004RNJ]

Multisim 14.1 Base Edition Components

1 mF [TAJV108K004RNJ]	1 mF [TPSV108K004R003 5]	1 mH [SDR1005- 102KL]	1 mH [SRR0906- 102YL]
1 mF [TAJV108K006RNJ]	1 mF [TPSV108K004R004 0]	1 mH [SDR1006- 102KL]	1 mH [SRR0908- 102YL]
1 mF [TPMD108K004R00 25]	1 mF [TPSV108K004R005 0]	1 mH [SDR1030- 102K]	1 mH [SRR1005- 102K]
1 mF [TPMD108K004R00 45]	1 mF [TPSV108K006R004 0]	1 mH [SDR1045- 102K]	1 mH [SRR1206- 102KL]
1 mF [TPME108K004R00 18]	1 mF [TPSV108K006R005 0]	1 mH [SDR1305- 102K]	1 mH [SRR1208- 102KL]
1 mF [TPME108K004R00 23]	1 mF [TRME108K004R00 23]	1 mH [SDR1307- 102KL]	1 mH [SRR1210- 102M]
1 mF [TPME108K004R00 23]	1 mF [TRME108K004R00 23]	1 mH [SDR1307A- 102K]	1 mH [SRR1210A- 102M]
1 mF [TPMV108K004R00 18]	1 mH [SDR0302- 102KL]	1 mH [SDR1806- 102KL]	1 mH [SRR1240- 102K]
1 mF [TPSE108K002R003 0]	1 mH [SDR0403- 102KL]	1 mH [SDR6603- 102M]	1 mH [SRR1260- 102K]
1 mF [TPSE108K002R004 0]	1 mH [SDR0503- 102KL]	1 mH [SDR7030- 102K]	1 mH [SRR1260A- 102K]
1 mF [TPSE108K004R004 0]	1 mH [SDR0604- 102KL]	1 mH [SDR7045- 102K]	1 mH [SRR1280- 102K]
1 mF [TPSE108K004R004 0]	1 mH [SDR0703- 102KL]	1 mH [SRR0603- 102KL]	1 mH [SRR1806- 102M]
1 mF [TPSE108K004R006 0]	1 mH [SDR0805- 102KL]	1 mH [SRR0604- 102KL]	1 mH [SRR6028- 102Y]
1 mF [TPSV108K004R002 5]	1 mH [SDR0906- 102KL]	1 mH [SRR0745A- 102M]	1 mH [SRR6603- 102ML]
		1 mH [SRR0805- 102K]	1 mH [SRR7032- 102M]

Multisim 14.1 Base Edition Components

1 mH [SRR7045-102M]	1 MOhm [4306R-102-105LF]	1 MOhm [4310R-102-105]	1 MOhm [4606X-AP2-105LF]
1 MOhm [4114R-1-105]	1 MOhm [4308H-101-105]	1 MOhm [4310R-102-105LF]	1 MOhm [4607M-101-105LF]
1 MOhm [4114R-1-105LF]	1 MOhm [4308M-102-105]	1 MOhm [4311R-101-105LF]	1 MOhm [4607X-101-105LF]
1 MOhm [4114R-2-105]	1 MOhm [4308R-101-105]	1 MOhm [4416P-1-105]	1 MOhm [4608X-101-105LF]
1 MOhm [4114R-2-105LF]	1 MOhm [4308R-101-105LF]	1 MOhm [4416P-2-105]	1 MOhm [4608X-102-105LF]
1 MOhm [4116R-1-105]	1 MOhm [4308R-102-105]	1 MOhm [4416P-T01-105]	1 MOhm [4608X-AP1-105LF]
1 MOhm [4116R-1-105LF]	1 MOhm [4308R-102-105LF]	1 MOhm [4416P-T02-105]	1 MOhm [4608X-AP2-105LF]
1 MOhm [4116R-2-105]	1 MOhm [4309R-101-105]	1 MOhm [4420P-T01-105]	1 MOhm [4609M-101-105LF]
1 MOhm [4116R-2-105LF]	1 MOhm [4309R-101-105LF]	1 MOhm [4604X-101-105LF]	1 MOhm [4609X-101-105LF]
1 MOhm [4306H-101-105]	1 MOhm [4310H-102-105]	1 MOhm [4604X-102-105LF]	1 MOhm [4610X-101-105LF]
1 MOhm [4306H-101-105LF]	1 MOhm [4310H-102-105LF]	1 MOhm [4605X-101-105LF]	1 MOhm [4610X-102-105LF]
1 MOhm [4306M-102-105]	1 MOhm [4310M-102-105]	1 MOhm [4605X-AP1-105LF]	1 MOhm [4610X-AP2-105LF]
1 MOhm [4306R-101-105]	1 MOhm [4310M-102-105LF]	1 MOhm [4606M-102-105LF]	1 MOhm [4611X-101-105LF]
1 MOhm [4306R-101-105LF]	1 MOhm [4310R-101-105]	1 MOhm [4606X-101-105LF]	1 MOhm [4612X-102-105LF]
1 MOhm [4306R-102-105]	1 MOhm [4310R-101-105LF]	1 MOhm [4606X-102-105LF]	1 MOhm [4614X-102-105LF]

Multisim 14.1 Base Edition Components

1 MOhm [4814P-1-105]	1 MOhm [4818P-2-105]	1 MOhm [CAY16-105J4GLF]	1 MOhm [CR0201-FW-1004GLF]
1 MOhm [4814P-1-105LF]	1 MOhm [4820P-1-105]	1 MOhm [CAY16-105J4LF]	1 MOhm [CR0402-FX-1004GLF]
1 MOhm [4814P-2-105]	1 MOhm [4820P-2-105]	1 MOhm [CAY16-105J8LF]	1 MOhm [CR0402-JW-105GLF]
1 MOhm [4814P-2-105LF]	1 MOhm [4820P-2-105F]	1 MOhm [CHV0603-JW-105ELF]	1 MOhm [CR0603-FX-1004ELF]
1 MOhm [4814P-T01-105]	1 MOhm [4820P-T01-105]	1 MOhm [CHV0805-FX-1004ELF]	1 MOhm [CR0603-JW-105ELF]
1 MOhm [4814P-T01-105LF]	1 MOhm [4820P-T02-105]	1 MOhm [CHV0805-JW-105ELF]	1 MOhm [CR0603-JW-105GLF]
1 MOhm [4814P-T02-105]	1 MOhm [CAT10-105J4LF]	1 MOhm [CHV1206-FW-1004ELF]	1 MOhm [CR0805-FX-1004ELF]
1 MOhm [4816P-1-105]	1 MOhm [CAT16-1004F4LF]	1 MOhm [CHV1206-FX-1004ELF]	1 MOhm [CR0805-JW-105ELF]
1 MOhm [4816P-1-105LF]	1 MOhm [CAT16-105J2LF]	1 MOhm [CHV1206-JW-105ELF]	1 MOhm [CR1206-FX-1004ELF]
1 MOhm [4816P-2-105]	1 MOhm [CAT16-105J4LF]	1 MOhm [CHV2010-FW-1004ELF]	1 MOhm [CR1206-JW-105ELF]
1 MOhm [4816P-2-105LF]	1 MOhm [CAT16-105J8LF]	1 MOhm [CHV2512-FX-1004ELF]	1 MOhm [CR1206-JW-105GLF]
1 MOhm [4816P-T01-105]	1 MOhm [CAT25-105JALF]	1 MOhm [CHV2512-JW-105ELF]	1 mOhm [CRE2512-FZ-R001E-2]
1 MOhm [4816P-T01-105LF]	1 MOhm [CAY10-105J4LF]	1 MOhm [CHV2512-JW-105ELF]	1 mOhm [CRE2512-FZ-R001E-3]
1 MOhm [4816P-T02-105]	1 MOhm [CAY16-1004F4LF]	1 MOhm [CHV2512-JW-105ELF]	1 mOhm [CRF2512-FV-R001ELF]
1 MOhm [4816P-T02-105LF]	1 MOhm [CAY16-105J2LF]		1 mOhm [CRF2512-JV-R001ELF]

Multisim 14.1 Base Edition Components

1 MOhm [CRM1206-FX-1004ELF]	1 MOhm [CRT0805-DY-1004ELF]	1 nF [C0402C102K1HACT U]	1 nF [C0603C102K2RACT U]
1 MOhm [CRM1206-JW-105ELF]	1 MOhm [CRT1206-BW-1004ELF]	1 nF [C0402C102K3GACT U]	1 nF [C0603C102K3GACT U]
1 MOhm [CRM2512-FX-1004ELF]	1 MOhm [CRT1206-BY-1004ELF]	1 nF [C0402C102K3HACT U]	1 nF [C0603C102K3HACT U]
1 MOhm [CRM2512-JW-105ELF]	1 MOhm [CRT1206-DY-1004ELF]	1 nF [C0402C102K3RACT U]	1 nF [C0603C102K3RACT U]
1 MOhm [CRS0805-FX-1004ELF]	1 MOhm [CRT1206-FZ-1004ELF]	1 nF [C0402C102K4RACT U]	1 nF [C0603C102K4GACT U]
1 MOhm [CRS1206-FX-1004ELF]	1 mOhm [CST0612-FC-R001E]	1 nF [C0402C102K5HACT U]	1 nF [C0603C102K4RACT U]
1 MOhm [CRS2010-FX-1004ELF]	1 nF [03063C102KAT2A]	1 nF [C0402C102K5RACT U]	1 nF [C0603C102K5GACT U]
1 MOhm [CRS2512-FX-1004ELF]	1 nF [03066C102KAT2A]	1 nF [C0402C102K8RACT U]	1 nF [C0603C102K5HACT U]
1 MOhm [CRT0603-BZ-1004ELF]	1 nF [0306ZC102KAT2A]	1 nF [C0402C102K9RACT U]	1 nF [C0603C102K5RACT U]
1 MOhm [CRT0603-DZ-1004ELF]	1 nF [05083C102KAT2S]	1 nF [C0603C102K1HACT U]	1 nF [C0603C102K8RACT U]
1 MOhm [CRT0805-BY-1004ELF]	1 nF [06123C102KAT2S]	1 nF [C0603C102K1RACT U]	1 nF [C0603C102K9RACT U]

Multisim 14.1 Base Edition Components

1 nF [C0805C102K1GACT U]	1 nF [C1206C102K1RACT U]	1 nF [C1210C102KBGAC TU]	1 nF [C2225C102KBGAC TU]
1 nF [C0805C102K1RACT U]	1 nF [C1206C102K2GACT U]	1 nF [C1210C102KCGAC TU]	1 nF [CA064C102K3RACT U]
1 nF [C0805C102K2RACT U]	1 nF [C1206C102K2RACT U]	1 nF [C1210C102KDGAC TU]	1 nF [CA064C102K4RACT U]
1 nF [C0805C102K3GACT U]	1 nF [C1206C102K3RACT U]	1 nF [C1812C102K1GACT U]	1 nF [CA064C102K5RACT U]
1 nF [C0805C102K3RACT U]	1 nF [C1206C102K4RACT U]	1 nF [C1812C102K2GACT U]	1 nF [CA064C102K8RACT U]
1 nF [C0805C102K4RACT U]	1 nF [C1206C102K5GACT U]	1 nF [C1812C102K5GACT U]	1 nF [GMC5.7102K100J3 1TR12]
1 nF [C0805C102K5GACT U]	1 nF [C1206C102K5RACT U]	1 nF [C1812C102KBGAC TU]	1 nF [GMC5.7102K50J31 TR12]
1 nF [C0805C102K5RACT U]	1 nF [C1206C102KCGAC TU]	1 nF [C1812C102KCGAC TU]	1 nF [GMC5.7103K250J3 1TR12]
1 nF [C0805C102K8RACT U]	1 nF [C1210C102K1GACT U]	1 nF [C1812C102KDGAC TU]	1 nF [GMC7.3102K100K3 1TR12]
1 nF [C0805C102KARACT U]	1 nF [C1210C102K2GACT U]	1 nF [C1825C102KBGAC TU]	1 nF [GMC7.3102K63K31 TR12]
1 nF [C1206C102K1GACT U]	1 nF [C1210C102K5GACT U]	1 nF [C2220C102KBGAC TU]	1 nF [GMC7.3103K250K3 1TR12]

Multisim 14.1 Base Edition Components

1 nF [GMC7.3103K63K31 TR12]	1 nF [MMC7.3102K100K 31TR12]	1 Ohm [CR0805-J/- 1R0ELF]	1 Ohm [CRM2010- JW-1R0ELF]
1 nF [GPC7.3102K160K3 1TR12]	1 nF [MMC7.3102K250K 31TR12]	1 Ohm [CR1206-J/- 1R0ELF]	1 Ohm [CRM2512- FX-1R00ELF]
1 nF [GPC7.3102K630K3 1TR12]	1 nF [MMC7.3102K400K 31TR12]	1 Ohm [CR1206-J/- 1R0GLF]	1 Ohm [CRM2512- JW-1R0ELF]
1 nF [GPC7.3102K63K31 TR12]	1 nF [MMC7.3102K50K3 1TR12]	1 Ohm [CR2010-J/- 1R0ELF]	1 Ohm [CRS0805- FW-1R00ELF]
1 nF [LD163C102KAB2A]	1 nF [MMC7.3102K63K3 1TR12]	1 Ohm [CR2512-J/- 1R0ELF]	1 Ohm [CRS1206- FW-1R00ELF]
1 nF [LD16YC102KAB2A]	1 nF [SPC7.3102K63K31 TR12]	1 Ohm [CRL0603- FW-1R00ELF]	1 Ohm [CRS2512- FW-1R00ELF]
1 nF [LD173C102KAB2S]	1 nF [SPC7.3102K100K31 TR12]	1 Ohm [CRL0805- FW-1R00ELF]	1 Ohm [CRT0805- CY-1R00ELF]
1 nF [LD175C102KAB2V]	1 nF [SPC7.3102K250K31 TR12]	1 Ohm [CRL1206- FW-1R00ELF]	1 Ohm [CRT0805- DY-1R00ELF]
1 nF [LD17YC102KAB2S]	1 nF [SPC7.3102K400K31 TR12]	1 Ohm [CRL2010- FW-1R00ELF]	1 Ohm [CRT0805- FY-1R00ELF]
1 nF [MMC5.7102K100J 31TR12]	1 nF [SPC7.3102K630K31 TR12]	1 Ohm [CRL2010- JW-1R00ELF]	1 Ohm [PWR163S- 25-1R00F]
1 nF [MMC5.7102K250J 31TR12]	1 nF [W2F15C1028AT1A]	1 Ohm [CRL2512- FW-1R00ELF]	1 Ohm [PWR163S- 25-1R00FE]
1 nF [MMC5.7102K50J3 1TR12]	1 Ohm [CR0402-J/- 1R0GLF]	1 Ohm [CRL2512- JW-1R00ELF]	1 Ohm [PWR163S- 25-1R00J]
	1 Ohm [CR0603-J/- 1R0ELF]	1 Ohm [CRM0805- JW-1R0ELF]	1 Ohm [PWR163S- 25-1R00JE]
		1 Ohm [CRM1206- FX-1R00ELF]	1 Ohm [PWR1913W1R00J]
		1 Ohm [CRM1206- JW-1R0ELF]	1 Ohm [PWR2010W1R00JE]

Multisim 14.1 Base Edition Components

1 Ohm [PWR220T-20-1R00F]	1 Ohm [PWR4318W1R00JE]	1 uF [C0603C105K4PACTU]	1 uF [C0805C105K8RACTU]
1 Ohm [PWR220T-20-1R00J]	1 Ohm [PWR4525W1R00JE]	1 uF [C0603C105K4RACTU]	1 uF [C0805C105K9PACTU]
1 Ohm [PWR220T-35-1R00F]	1 Ohm [PWR5322W1R00JE]	1 uF [C0603C105K8PACTU]	1 uF [C0805C105K9RACTU]
1 Ohm [PWR221T-30-1R00F]	1 Ohm [PWR6327W1R00F]	1 uF [C0603C105K8RACTU]	1 uF [C0805C105M3VAC TU]
1 Ohm [PWR221T-30-1R00J]	1 Ohm [PWR6327W1R00JE]	1 uF [C0603C105K9PACTU]	1 uF [C0805C105M4VAC TU]
1 Ohm [PWR2615N1R00F]	1 uF [05086C105KAT2A]	1 uF [C0603C105K9RACTU]	1 uF [C0805C105M8VAC TU]
1 Ohm [PWR2615W1R00F]	1 uF [0508ZC105KAT2A]	1 uF [C0805C105K3PACTU]	1 uF [C1206C105K3NAC TU]
1 Ohm [PWR2615W1R00J]	1 uF [06126C105KAT2V]	1 uF [C0805C105K4PACTU]	1 uF [C1206C105K3PACTU]
1 Ohm [PWR263S-20-1R00F]	1 uF [0612YC105KAT2A]	1 uF [C0805C105K4RACTU]	1 uF [C1206C105K3RACTU]
1 Ohm [PWR263S-20-1R00J]	1 uF [0612ZC105KAT2V]	1 uF [C0805C105K8NAC TU]	1 uF [C1206C105K4RACTU]
1 Ohm [PWR263S-35-1R00F]	1 uF [C0402C105K8PACTU]	1 uF [C0805C105K8PACTU]	1 uF [C1206C105K5RACTU]
1 Ohm [PWR263S-35-1R00FE]	1 uF [C0402C105K9PACTU]		
1 Ohm [PWR263S-35-1R00J]	1 uF [C0603C105K3PACTU]		
1 Ohm [PWR3014W1R00JE]			

Multisim 14.1 Base Edition Components

1 uF [C1206C105K8RACT U]	1 uF [C1210C105K5NAC TU]	1 uF [C1812C105K5RACT U]	1 uF [C2220C105KARACT U]
1 uF [C1206C105K9RACT U]	1 uF [C1210C105K5PACT U]	1 uF [C1812C105M5UAC TU]	1 uF [C2225C105K1RACT U]
1 uF [C1206C105M3VAC TU]	1 uF [C1210C105K5RACT U]	1 uF [C1812F105K1RACT U]	1 uF [C2225C105K5RACT U]
1 uF [C1206C105M4VAC TU]	1 uF [C1210C105K8RACT U]	1 uF [C1812F105K3RACT U]	1 uF [C2225C105KARACT U]
1 uF [C1206C105M8VAC TU]	1 uF [C1210C105K9RACT U]	1 uF [C1812F105K5RACT U]	1 uF [C2225C105M5UAC TU]
1 uF [C1206F105K4RACT U]	1 uF [C1210C105M3VAC TU]	1 uF [C1825C105K2RACT U]	1 uF [LD17ZC105KAB2A]
1 uF [C1210C105K1RACT U]	1 uF [C1210C105M5UAC TU]	1 uF [C1825C105K5RACT U]	1 uF [LD18YC105KAB2A]
1 uF [C1210C105K3PACT U]	1 uF [C1210C105M8VAC TU]	1 uF [C1825C105KARACT U]	1 uF [LD18ZC105KAB2V]
1 uF [C1210C105K3RACT U]	1 uF [C1210F105K3RACT U]	1 uF [C1825C105M5UAC TU]	1 uF [MDC10105K100A5 2P3TUBE]
1 uF [C1210C105K4PACT U]	1 uF [C1210F105K4RACT U]	1 uF [C2220C105K5R1C7 186]	1 uF [MDC10105K250A5 7P7TUBE]
1 uF [C1210C105K4RACT U]	1 uF [C1812C105K3RACT U]	1 uF [C2220C105K5RACT U]	1 uF [MDC10105K250A5 7P8TUBE]

Multisim 14.1 Base Edition Components

1 uF [MDC10105K50A52 P3TUBE]	1 uF [T491A105M025AT]	1 uF [T494C105M050AT]	1 uF [TAJA105K016RNJ]
1 uF [MDC15105K100B5 3P3TUBE]	1 uF [T491A105M035AT]	1 uF [T494S105M020AT]	1 uF [TAJA105K020RNJ]
1 uF [MDC15105K50B53 P3TUBE]	1 uF [T491B105M025AT]	1 uF [T494V105M050AT]	1 uF [TAJA105K025RNJ]
1 uF [MDK10105K50A52 P3TUBE]	1 uF [T491B105M035AT]	1 uF [T495A105M020AT E3K0]	1 uF [TAJA105K035RNJ]
1 uF [MDS10105K100A5 2P3TUBE]	1 uF [T491B105M050AT]	1 uF [T495A105M035AT E3K0]	1 uF [TAJB105K035RNJ]
1 uF [MDS10105K50A52 P3TUBE]	1 uF [T491C105M050AT]	1 uF [T495B105M035AT E1K7]	1 uF [TAJB105K050RNJ]
1 uF [MDS15105K100B5 3P3TUBE]	1 uF [T491V105M050AT]	1 uF [T497A105M015AT 6110]	1 uF [TAJP105K025RNJ]
1 uF [PGC26D105MAB2S 1]	1 uF [T494A105M016AT]	1 uF [T498A105M016AT E6K5]	1 uF [TAJP105K035RNJ]
1 uF [T409C105M025AH 4250]	1 uF [T494A105M020AT]	1 uF [T498A105M020AT E5K9]	1 uF [TAJR105K010RNJ]
1 uF [T489A105M025AT E6K6]	1 uF [T494A105M025AT]	1 uF [T498A105M035AT E10K]	1 uF [TAJR105K016RNJ]
1 uF [T491A105M016AT]	1 uF [T494B105M025AT]	1 uF [TACL105K006RTA]	1 uF [TAJR105K020RNJ]
1 uF [T491A105M020AT]	1 uF [T494B105M035AT]	1 uF [TACL105K010RTA]	1 uF [TAJR105K025RNJ]
	1 uF [T494B105M050AT]	1 uF [TACL105K016RTA]	1 uF [TAJS105K010RNJ]
			1 uF [TAJS105K016RNJ]

Multisim 14.1 Base Edition Components

1 uF [TAJS105K020RNJ]	1 uF [TPSB105K050R300 0]	1 uH [SDR0302- 1R0ML]	1 uH [SRN4026- 1R0Y]
1 uF [TAJS105K025RNJ]	1 uF [TPSC105K050R250 0]	1 uH [SDR0403- 1R0ML]	1 uH [SRN5020- 1R0Y]
1 uF [TAJS105K035RNJ]	1 uF [TPSR105K010R900 0]	1 uH [SDR0703- 1R0ML]	1 uH [SRN6045- 1R0Y]
1 uF [TAJT105K016RNJ]	1 uF [TPSR105K020R600 0]	1 uH [SDR1806- 1R0ML]	1 uH [SRP1038A- 1R0M]
1 uF [TAJT105K020RNJ]	1 uF [TPSS105K020R600 0]	1 uH [SDR6603- 1R0M]	1 uH [SRP1040- 1R0M]
1 uF [TAJT105K035RNJ]	1 uF [TPST105K020R200 0]	1 uH [SDR7030- 1R0M]	1 uH [SRP1235- 1R0M]
1 uF [TAJW105K050RNJ]	1 uF [TRJA105K020RRJ]	1 uH [SRN2010- 1R0M]	1 uH [SRP1245A- 1R0M]
1 uF [THJA105K025RJN]	1 uF [TRJA105K025RRJ]	1 uH [SRN2012- 1R0M]	1 uH [SRP1250- 1R0M]
1 uF [THJA105K035RJN]	1 uF [TRJB105K035RRJ]	1 uH [SRN2510- 1R0M]	1 uH [SRP1265A- 1R0M]
1 uF [THJB105K035RJN]	1 uF [TRJC105K050RRJ]	1 uH [SRN2512- 1R0M]	1 uH [SRP1270- 1R0M]
1 uF [TPSA105K020R300 0]	1 uF [W3L16C105MAT1 A]	1 uH [SRN3010- 1R0Y]	1 uH [SRP1770TA- 1R0M]
1 uF [TPSA105K025R400 0]	1 uH [SDE0403A- 1R0M]	1 uH [SRN3015- 1R0Y]	1 uH [SRP4012- 1R0M]
1 uF [TPSA105K035R300 0]		1 uH [SRN4012T- 1R0M]	1 uH [SRP4012TA- 1R0M]
1 uF [TPSB105K035R200 0]		1 uH [SRN4018- 1R0Y]	1 uH [SRP4020- 1R0M]

Multisim 14.1 Base Edition Components

1 uH [SRP4020TA-1ROM]	1 uH [SRR6040A-1ROY]	1.02 kOhm [CR1206-FX-1021ELF]	1.07 kOhm [CR0805-FX-1071ELF]
1 uH [SRP5015TA-1ROM]	1 uH [SRR6603-1ROML]	1.02 kOhm [CRT1206-BY-1021ELF]	1.07 kOhm [CR1206-FX-1071ELF]
1 uH [SRP5030T-1ROM]	1 uH [SRR7045-1ROM]	1.02 MOhm [CR1206-FW-1024ELF]	1.07 kOhm [CR2010-FX-1071ELF]
1 uH [SRP5030TA-1ROM]	1 uH [SRU1028-1ROY]	1.05 kOhm [CR0402-FX-1051GLF]	1.07 MOhm [CR1206-FW-1074ELF]
1 uH [SRP6540-1ROM]	1 uH [SRU1028A-1ROY]	1.05 kOhm [CR0603-FX-1051ELF]	1.1 kOhm [4310R-101-112]
1 uH [SRP7028A-1ROM]	1 uH [SRU2009-1ROY]	1.05 kOhm [CR0805-FX-1051ELF]	1.1 kOhm [4605X-101-112LF]
1 uH [SRP7030-1ROFM]	1 uH [SRU2011-1ROY]	1.05 kOhm [CR1206-FX-1051ELF]	1.1 kOhm [CAT16-1101F4LF]
1 uH [SRP7050TA-1ROM]	1 uH [SRU2013-1ROY]	1.05 kOhm [CR1206-FX-1051ELF]	1.1 kOhm [CAT16-112J4LF]
1 uH [SRR1005-1ROM]	1 uH [SRU2016-1ROY]	1.05 kOhm [CRT0603-BY-1051ELF]	1.1 kOhm [CAY16-112J4LF]
1 uH [SRR1210-1ROY]	1 uH [SRU5018-1ROY]	1.05 kOhm [CRT0805-BY-1051ELF]	1.1 kOhm [CR0603-FX-1101ELF]
1 uH [SRR1210A-1ROY]	1 uH [SRU8028-1ROY]	1.07 kOhm [CR0402-FX-1071GLF]	1.1 kOhm [CR0603-JW-112ELF]
1 uH [SRR1240-1ROY]	1.02 kOhm [CR0402-FX-1021GLF]	1.07 kOhm [CR0805-FX-1101ELF]	1.1 kOhm [CR0805-FX-1101ELF]
1 uH [SRR1260-1ROY]	1.02 kOhm [CR0603-FX-1021ELF]	1.07 kOhm [CR0805-FX-1101ELF]	1.1 kOhm [CR0805-FX-1101ELF]
1 uH [SRR1260A-1ROY]	1.02 kOhm [CR0805-FX-1021ELF]		
1 uH [SRR4018-1ROY]			

Multisim 14.1 Base Edition Components

1.1 kOhm [CR1206-FX-1101ELF]	1.1 MOhm [CR1206-FW-1104ELF]	1.1 nF [C2225C112KBGAC TU]	1.1 uH [SRP7030-1R1FM]
1.1 kOhm [CR1206-JW-112ELF]	1.1 MOhm [CR1206-JW-115ELF]	1.1 nF [CDR33BP112BKSM]	1.1 uH [SRR1280-1R1Y]
1.1 kOhm [CR2512-JW-112ELF]	1.1 nF [C0402C112K3HACT U]	1.1 Ohm [CR0805-J/-1R1ELF]	1.13 kOhm [CR0201-FW-1131GLF]
1.1 kOhm [CRT0402-FZ-1101GLF]	1.1 nF [C0402C112K5HACT U]	1.1 Ohm [CR1206-J/-1R1ELF]	1.13 kOhm [CR0402-FX-1131GLF]
1.1 kOhm [CRT0603-BY-1101ELF]	1.1 nF [C0603C112K1HACT U]	1.1 Ohm [CRL0603-FW-1R10ELF]	1.13 kOhm [CR0603-FX-1131ELF]
1.1 kOhm [CRT0805-BY-1101ELF]	1.1 nF [C0603C112K3HACT U]	1.1 Ohm [CRL0805-FW-1R10ELF]	1.13 kOhm [CR0805-FX-1131ELF]
1.1 kOhm [CRT0805-DY-1101ELF]	1.1 nF [C0603C112K5HACT U]	1.1 Ohm [CRL1206-FW-1R10ELF]	1.13 kOhm [CRM2512-FX-1131ELF]
1.1 kOhm [CRT0805-FY-1101ELF]	1.1 nF [C1210C112KBGAC TU]	1.1 Ohm [CRL2010-FW-1R10ELF]	1.13 kOhm [CRT0805-BY-1131ELF]
1.1 MOhm [CR0402-FW-1104GLF]	1.1 nF [C1812C112KBGAC TU]	1.1 Ohm [CRL2010-JW-1R10ELF]	1.13 MOhm [CR1206-FW-1134ELF]
1.1 MOhm [CR0402-JW-115GLF]	1.1 nF [C1825C112KBGAC TU]	1.1 Ohm [CRL2512-FW-1R10ELF]	1.15 kOhm [CR0402-FX-1151GLF]
1.1 MOhm [CR0603-JW-115ELF]	1.1 nF [C2220C112KBGAC TU]	1.1 Ohm [PWR4318W1R10F]	1.15 kOhm [CR0603-FX-1151ELF]
1.1 MOhm [CR0805-JW-115ELF]			

Multisim 14.1 Base Edition Components

1.15 kOhm [CR0805-FX- 1151ELF]	1.2 kOhm [4116R- 2-122LF]	1.2 kOhm [4308M- 102-122]	1.2 kOhm [4310R- 101-122]
1.15 kOhm [CR1206-FX- 1151ELF]	1.2 kOhm [4306H- 101-122]	1.2 kOhm [4308M- 102-122LF]	1.2 kOhm [4310R- 101-122LF]
1.18 kOhm [CR0402-FX- 1181GLF]	1.2 kOhm [4306H- 101-122LF]	1.2 kOhm [4308R- 101-122]	1.2 kOhm [4310R- 102-122]
1.18 kOhm [CR0603-FX- 1181ELF]	1.2 kOhm [4306M- 101-122]	1.2 kOhm [4308R- 101-122LF]	1.2 kOhm [4310R- 102-122LF]
1.18 kOhm [CR0603-FX- 1181ELF]	1.2 kOhm [4306M- 101-122LF]	1.2 kOhm [4308R- 102-122]	1.2 kOhm [4416P- 1-122]
1.18 kOhm [CR0805-FX- 1181ELF]	1.2 kOhm [4306M- 102-122]	1.2 kOhm [4308R- 102-122LF]	1.2 kOhm [4416P- 2-122]
1.18 kOhm [CR0805-FX- 1181ELF]	1.2 kOhm [4306M- 102-122LF]	1.2 kOhm [4309R- 101-122]	1.2 kOhm [4416P- T01-122]
1.18 kOhm [CR1206-FX- 1181ELF]	1.2 kOhm [4306R- 101-122]	1.2 kOhm [4309R- 101-122LF]	1.2 kOhm [4420P- 1-122]
1.2 kOhm [4114R- 1-122]	1.2 kOhm [4306R- 101-122LF]	1.2 kOhm [4310H- 101-122]	1.2 kOhm [4420P- T01-122]
1.2 kOhm [4114R- 1-122LF]	1.2 kOhm [4306R- 102-122]	1.2 kOhm [4310H- 101-122LF]	1.2 kOhm [4420P- T02-122]
1.2 kOhm [4114R- 2-122]	1.2 kOhm [4306R- 102-122LF]	1.2 kOhm [4310H- 102-122]	1.2 kOhm [4604X- 101-122LF]
1.2 kOhm [4114R- 2-122LF]	1.2 kOhm [4308H- 102-122]	1.2 kOhm [4310H- 102-122LF]	1.2 kOhm [4604X- 102-122LF]
1.2 kOhm [4116R- 1-122]	1.2 kOhm [4308H- 102-122LF]	1.2 kOhm [4310M- 101-122]	1.2 kOhm [4605M- 101-122LF]
1.2 kOhm [4116R- 1-122LF]	1.2 kOhm [4308M- 101-122]	1.2 kOhm [4310M- 102-122]	1.2 kOhm [4605X- 101-122LF]
1.2 kOhm [4116R- 2-122]	1.2 kOhm [4308M- 101-122LF]	1.2 kOhm [4310M- 102-122LF]	1.2 kOhm [4606H- 101-122LF]

Multisim 14.1 Base Edition Components

1.2 kOhm [4606X-101-122LF]	1.2 kOhm [4611X-101-122LF]	1.2 kOhm [4818P-T02-122]	1.2 kOhm [CR0402-JW-122GLF]
1.2 kOhm [4606X-102-122LF]	1.2 kOhm [4612X-102-122LF]	1.2 kOhm [4820P-1-122]	1.2 kOhm [CR0603-FX-1201ELF]
1.2 kOhm [4606X-AP1-122LF]	1.2 kOhm [4614X-101-122LF]	1.2 kOhm [4820P-2-122]	1.2 kOhm [CR0603-JW-122ELF]
1.2 kOhm [4607X-101-122LF]	1.2 kOhm [4614X-102-122LF]	1.2 kOhm [4820P-2-122LF]	1.2 kOhm [CR0603-JW-122GLF]
1.2 kOhm [4608H-101-122LF]	1.2 kOhm [4814P-T01-122]	1.2 kOhm [4820P-T01-122]	1.2 kOhm [CR0805-FX-1201ELF]
1.2 kOhm [4608H-102-122LF]	1.2 kOhm [4814P-T02-122]	1.2 kOhm [CAT16-1201F4LF]	1.2 kOhm [CR0805-FX-1201GLF]
1.2 kOhm [4608X-101-122LF]	1.2 kOhm [4816P-1-122]	1.2 kOhm [CAT16-1201F8LF]	1.2 kOhm [CR0805-JW-122ELF]
1.2 kOhm [4608X-102-122LF]	1.2 kOhm [4816P-1-122LF]	1.2 kOhm [CAT16-122J4LF]	1.2 kOhm [CR1206-FX-1201ELF]
1.2 kOhm [4609H-101-122LF]	1.2 kOhm [4816P-2-122]	1.2 kOhm [CAT25-122JALF]	1.2 kOhm [CR1206-JW-122ELF]
1.2 kOhm [4609X-101-122LF]	1.2 kOhm [4816P-2-122LF]	1.2 kOhm [CAY10-122J4LF]	1.2 kOhm [CR2010-JW-122ELF]
1.2 kOhm [4610H-101-122LF]	1.2 kOhm [4816P-T01-122]	1.2 kOhm [CAY16-1201F4LF]	1.2 kOhm [CR2512-JW-122ELF]
1.2 kOhm [4610H-102-122LF]	1.2 kOhm [4816P-T01-122LF]	1.2 kOhm [CAY16-122J4LF]	1.2 kOhm [CRM1206-JW-122ELF]
1.2 kOhm [4610X-101-122LF]	1.2 kOhm [4816P-T02-122]	1.2 kOhm [CAY16-122J8LF]	1.2 kOhm [CRT0805-BY-1201ELF]
1.2 kOhm [4610X-102-122LF]	1.2 kOhm [4816P-T02-122LF]	1.2 kOhm [CAY17-122JALF]	1.2 kOhm [PWR163S-25-1201J]
1.2 kOhm [4610X-AP1-122LF]	1.2 kOhm [4818P-2-122]	1.2 kOhm [CR0402-FX-1201GLF]	

Multisim 14.1 Base Edition Components

1.2 kOhm [PWR163S-25-1201JE]	1.2 MOhm [4608X-102-125LF]	1.2 nF [C0402C122K5RACTU]	1.2 nF [C0805C122K3GACTU]
1.2 kOhm [PWR263S-35-1201J]	1.2 MOhm [CAT25-125JALF]	1.2 nF [C0603C122K1HACTU]	1.2 nF [C0805C122K4RACTU]
1.2 kOhm [PWR263S-35-1201JE]	1.2 MOhm [CR0402-JW-125GLF]	1.2 nF [C0603C122K1RACTU]	1.2 nF [C0805C122K5GACTU]
1.2 mF [4SVPC1200M]	1.2 MOhm [CR0603-JW-125ELF]	1.2 nF [C0603C122K3HACTU]	1.2 nF [C0805C122K5RACTU]
1.2 mH [SDR0302-122KL]	1.2 MOhm [CR0805-FX-1204ELF]	1.2 nF [C0603C122K3RACTU]	1.2 nF [C0805C122KARACTU]
1.2 mH [SDR0503-122JL]	1.2 MOhm [CR0805-JW-125ELF]	1.2 nF [C0603C122K4RACTU]	1.2 nF [C1206C122K1GACTU]
1.2 mH [SDR0805-122KL]	1.2 MOhm [CR1206-FW-1204ELF]	1.2 nF [C0603C122K5HACTU]	1.2 nF [C1206C122K1RACTU]
1.2 mH [SDR0906-122KL]	1.2 MOhm [CR1206-JW-125ELF]	1.2 nF [C0603C122K5RACTU]	1.2 nF [C1206C122K2GACTU]
1.2 mH [SRR0906-122YL]	1.2 nF [C0402C122K3HACTU]	1.2 nF [C0805C122K1GACTU]	1.2 nF [C1206C122K2RACTU]
1.2 mH [SRR1005-122K]	1.2 nF [C0402C122K3RACTU]	1.2 nF [C0805C122K1RACTU]	1.2 nF [C1206C122K5GACTU]
1.2 mH [SRR1206-122KL]	1.2 nF [C0402C122K4RACTU]	1.2 nF [C0805C122K2RACTU]	
1.2 MOhm [4116R-1-125LF]	1.2 nF [C0402C122K5HACTU]		

Multisim 14.1 Base Edition Components

1.2 nF [C1210C122KBGAC TU]	1.2 nF [GMC7.3123K400K3 5TR12]	1.2 Ohm [CR1206- J/-1R2ELF]	1.2 uF [C0805C125K4RACT U]
1.2 nF [C1812C122KBGAC TU]	1.2 nF [MMC5.7122K100J 31TR12]	1.2 Ohm [CR2010- J/-1R2ELF]	1.2 uF [C0805C125K8PACT U]
1.2 nF [C1825C122KBGAC TU]	1.2 nF [MMC5.7122K250J 31TR12]	1.2 Ohm [CRL0603- FW-1R20ELF]	1.2 uF [C0805C125K8RACT U]
1.2 nF [C2220C122KBGAC TU]	1.2 nF [MMC5.7122K50J3 1TR12]	1.2 Ohm [CRL0603- JW-1R20ELF]	1.2 uF [C0805C125K9PACT U]
1.2 nF [C2225C122KBGAC TU]	1.2 nF [MMC7.3122K100K 31TR12]	1.2 Ohm [CRL0805- FW-1R20ELF]	1.2 uF [C0805C125K9RACT U]
1.2 nF [GMC5.7122K100J3 1TR12]	1.2 nF [MMC7.3122K250K 31TR12]	1.2 Ohm [CRL1206- FW-1R20ELF]	1.2 uF [C1206C125K3RACT U]
1.2 nF [GMC5.7122K50J31 TR12]	1.2 nF [MMC7.3122K400K 31TR12]	1.2 Ohm [CRL2010- FW-1R20ELF]	1.2 uF [C1206C125K4RACT U]
1.2 nF [GMC5.7123K250J3 3TR12]	1.2 nF [MMC7.3122K50K3 1TR12]	1.2 Ohm [CRL2010- JW-1R20ELF]	1.2 uF [C1206C125K8RACT U]
1.2 nF [GMC7.3122K100K3 1TR12]	1.2 nF [MMC7.3122K63K3 1TR12]	1.2 Ohm [CRL2512- FW-1R20ELF]	1.2 uF [C1210C125K3PACT U]
1.2 nF [GMC7.3122K400K3 1TR12]	1.2 Ohm [CR0402- J/-1R2GLF]	1.2 Ohm [CRM2512-JW- 1R2ELF]	1.2 uF [C1210C125K3RACT U]
1.2 nF [GMC7.3123K100K3 1TR12]	1.2 Ohm [CR0603- J/-1R2ELF]	1.2 Ohm [CRT0402- FZ-1R20GLF]	1.2 uF [C1210C125K3RACT U]
	1.2 Ohm [CR0805- J/-1R2ELF]	1.2 Ohm [PWR6327W1R20F]	1.2 uF [C1210F125K4RACT U]
		1.2 uF [C0805C125K4PACT U]	

Multisim 14.1 Base Edition Components

1.2 uF [C1825C125K5RACT U]	1.2 uF [MDK15125K50B53 P3TUBE]	1.2 uH [SRP4020TA-1R2M]	1.2 uH [SRU6025A- 1R2Y]
1.2 uF [C1825C125M5UAC TU]	1.2 uH [SDE0604A- 1R2M]	1.2 uH [SRP5030T- 1R2M]	1.21 kOhm [CR0402-FX- 1211GLF]
1.2 uF [C2220C125K5RACT U]	1.2 uH [SDR0302- 1R2ML]	1.2 uH [SRP5030TA-1R2M]	1.21 kOhm [CR0603-FX- 1211ELF]
1.2 uF [C2225C125KARACT U]	1.2 uH [SDR0604- 1R2ML]	1.2 uH [SRP7050TA-1R2M]	1.21 kOhm [CR0805-FX- 1211ELF]
1.2 uF [MDC10125K100A5 2P3TUBE]	1.2 uH [SDR0703- 1R2ML]	1.2 uH [SRR1260- 1R2Y]	1.21 kOhm [CR1206-FX- 1211ELF]
1.2 uF [MDC10125K250A5 8P7TUBE]	1.2 uH [SDR7045- 1R2M]	1.2 uH [SRR1260A- 1R2Y]	1.21 kOhm [CR2010-FX- 1211ELF]
1.2 uF [MDC10125K250A5 8P8TUBE]	1.2 uH [SRN3010- 1R2Y]	1.2 uH [SRR1280- 1R2Y]	1.21 kOhm [CRM1206-FX- 1211ELF]
1.2 uF [MDC10125K50A52 P3TUBE]	1.2 uH [SRN4018- 1R2Y]	1.2 uH [SRR4011- 1R2YL]	1.21 kOhm [CRT0402-FZ- 1211GLF]
1.2 uF [MDC15125K100B5 3P3TUBE]	1.2 uH [SRN4026- 1R2Y]	1.2 uH [SRR4028- 1R2Y]	1.21 kOhm [CRT0603-BY- 1211ELF]
1.2 uF [MDC15125K50B53 P3TUBE]	1.2 uH [SRP1040- 1R2M]	1.2 uH [SRR5018- 1R2Y]	1.21 MOhm [CR0402-FX- 1214GLF]
1.2 uF [MDK15125K100B5 3P3TUBE]	1.2 uH [SRP1235- 1R2M]	1.2 uH [SRU3014- 1R2Y]	
	1.2 uH [SRP1250- 1R2M]	1.2 uH [SRU5028- 1R2Y]	
	1.2 uH [SRP4012- 1R2M]	1.2 uH [SRU5028A- 1R2Y]	
	1.2 uH [SRP4012TA-1R2M]	1.2 uH [SRU6018- 1R2Y]	
	1.2 uH [SRP4020- 1R2M]	1.2 uH [SRU6025- 1R2Y]	

Multisim 14.1 Base Edition Components

1.21 MOhm [CR0603-FX- 1214ELF]	1.25 uH [SRP1205- 1R0Y]	1.3 kOhm [CAY16- 1301F4LF]	1.3 MOhm [CR0805-JW- 135ELF]
1.21 MOhm [CR0805-FX- 1214ELF]	1.27 kOhm [CR0402-FX- 1271GLF]	1.3 kOhm [CAY16- 132J4LF]	1.3 MOhm [CR1206-FW- 1304ELF]
1.21 Ohm [CRM1206-FX- 1R21ELF]	1.27 kOhm [CR0603-FX- 1271ELF]	1.3 kOhm [CR0402- FX-1301GLF]	1.3 MOhm [CR1206-JW- 135ELF]
1.24 kOhm [CR0402-FX- 1241GLF]	1.27 kOhm [CR0805-FX- 1271ELF]	1.3 kOhm [CR0603- FX-1301ELF]	1.3 nF [C0402C132K3HACT U]
1.24 kOhm [CR0603-FX- 1241ELF]	1.27 kOhm [CR1206-FX- 1271ELF]	1.3 kOhm [CR0603- JW-132ELF]	1.3 nF [C0402C132K5HACT U]
1.24 kOhm [CR0805-FX- 1241ELF]	1.27 kOhm [CRT0603-FZ- 1271ELF]	1.3 kOhm [CR0805- JW-132ELF]	1.3 nF [C0603C132K1HACT U]
1.24 kOhm [CR1206-FX- 1241ELF]	1.27 kOhm [CRT1206-BY- 1271ELF]	1.3 kOhm [CR1206- FX-1301ELF]	1.3 nF [C0603C132K3HACT U]
1.24 kOhm [CR1206-FX- 1241GLF]	1.3 kOhm [4308R- 101-132]	1.3 kOhm [CR1206- JW-132ELF]	1.3 nF [C0603C132K5HACT U]
1.24 kOhm [CRT0402-BV- 1241GLF]	1.3 kOhm [4608M- 102-132LF]	1.3 kOhm [CR2010- JW-132ELF]	1.3 nF [C1210C132KBGAC TU]
1.24 kOhm [CRT0805-CX- 1241ELF]	1.3 kOhm [4816P- 2-132]	1.3 MOhm [CR0402-JW- 135GLF]	1.3 nF [C1812C132KBGAC TU]
1.25 kOhm [PWR220T-35- 1251J]	1.3 kOhm [CAT16- 132J4LF]	1.3 MOhm [CR0603-JW- 135ELF]	1.3 nF [C1825C132KBGAC TU]

Multisim 14.1 Base Edition Components

1.3 nF [C2220C132KBGAC TU]	1.3 Ohm [CRM1206-JW- 1R3ELF]	1.33 kOhm [CRT0805-CX- 1331ELF]	1.4 kOhm [CRT0603-DZ- 1401ELF]
1.3 nF [C2225C132KBGAC TU]	1.3 Ohm [CRM2512-JW- 1R3ELF]	1.33 MOhm [CR0402-FX- 1334GLF]	1.4 kOhm [CRT0805-BY- 1401ELF]
1.3 Ohm [CR0805- J/-1R3ELF]	1.3 Ohm [PWR263S-20- 1R30F]	1.37 kOhm [CAT16- 1371F4LF]	1.4 uH [SDR0302- 1R4ML]
1.3 Ohm [CR1206- J/-1R3ELF]	1.3 uH [SRN6045- 1R3Y]	1.37 kOhm [CR0402-FX- 1371GLF]	1.4 uH [SDR0403- 1R4ML]
1.3 Ohm [CR2010- J/-1R3ELF]	1.3 uH [SRP1204- 1R1M]	1.37 kOhm [CR0603-FX- 1371ELF]	1.4 uH [SRP1045- 1R4M]
1.3 Ohm [CRL0603- FW-1R30ELF]	1.33 kOhm [CR0402-FX- 1331GLF]	1.37 kOhm [CR0805-FX- 1371ELF]	1.4 uH [SRR1280- 1R4Y]
1.3 Ohm [CRL0603- JW-1R30ELF]	1.33 kOhm [CR0603-FX- 1331ELF]	1.37 kOhm [CR1206-FX- 1371ELF]	1.4 uH [SRR1305- 1R4ZL]
1.3 Ohm [CRL0805- FW-1R30ELF]	1.33 kOhm [CR0805-FX- 1331ELF]	1.4 kOhm [4116R- 1-142]	1.43 kOhm [CR0402-FX- 1431GLF]
1.3 Ohm [CRL1206- FW-1R30ELF]	1.33 kOhm [CR1206-FX- 1331ELF]	1.4 kOhm [CR0402- FX-1401GLF]	1.43 kOhm [CR0603-FX- 1431ELF]
1.3 Ohm [CRL1206- JW-1R30ELF]	1.33 kOhm [CRT0402-FZ- 1331GLF]	1.4 kOhm [CR0603- FX-1401ELF]	1.43 kOhm [CR0805-FX- 1431ELF]
1.3 Ohm [CRL2010- FW-1R30ELF]	1.33 kOhm [CRT0603-BY- 1331ELF]	1.4 kOhm [CR1206- FX-1401ELF]	1.43 kOhm [CR1206-FX- 1431ELF]
1.3 Ohm [CRL2010- JW-1R30ELF]	1.33 kOhm [CRT0805-BY- 1331ELF]	1.4 kOhm [CRT0603-BY- 1401ELF]	1.47 kOhm [CR0402-FX- 1471GLF]

Multisim 14.1 Base Edition Components

1.47 kOhm [CR0603-FX- 1471ELF]	1.5 kOhm [4116R- 2-152]	1.5 kOhm [4308R- 102-152]	1.5 kOhm [4416P- T01-152]
1.47 kOhm [CR0805-FX- 1471ELF]	1.5 kOhm [4116R- 2-152LF]	1.5 kOhm [4308R- 102-152LF]	1.5 kOhm [4420P- 1-152]
1.47 kOhm [CR1206-FX- 1471ELF]	1.5 kOhm [4306H- 101-152LF]	1.5 kOhm [4309R- 101-152]	1.5 kOhm [4420P- 2-152]
1.47 kOhm [CR1206-FX- 1471ELF]	1.5 kOhm [4306M- 101-152]	1.5 kOhm [4309R- 101-152LF]	1.5 kOhm [4420P- T01-152]
1.47 kOhm [CRT0402-FZ- 1471GLF]	1.5 kOhm [4306M- 101-152LF]	1.5 kOhm [4310H- 101-152LF]	1.5 kOhm [4420P- T02-152]
1.47 kOhm [CRT0603-FZ- 1471ELF]	1.5 kOhm [4306R- 101-152]	1.5 kOhm [4310H- 102-152]	1.5 kOhm [4604X- 101-152LF]
1.47 kOhm [CRT0603-FZ- 1471ELF]	1.5 kOhm [4306R- 101-152LF]	1.5 kOhm [4310H- 102-152LF]	1.5 kOhm [4604X- 102-152LF]
1.47 kOhm [CRT0603-PW- 1471ELF]	1.5 kOhm [4306R- 102-152]	1.5 kOhm [4310M- 101-152]	1.5 kOhm [4605X- 101-152LF]
1.47 MOhm [CR1206-FW- 1474ELF]	1.5 kOhm [4306R- 102-152LF]	1.5 kOhm [4310M- 101-152LF]	1.5 kOhm [4605X- AP1-152LF]
1.5 kOhm [4114R- 1-152]	1.5 kOhm [4308H- 102-152]	1.5 kOhm [4310M- 102-152]	1.5 kOhm [4606X- 101-152LF]
1.5 kOhm [4114R- 1-152LF]	1.5 kOhm [4308H- 102-152LF]	1.5 kOhm [4310R- 101-152]	1.5 kOhm [4606X- 102-152LF]
1.5 kOhm [4114R- 2-152]	1.5 kOhm [4308M- 101-152]	1.5 kOhm [4310R- 101-152LF]	1.5 kOhm [4606X- AP2-152LF]
1.5 kOhm [4114R- 2-152LF]	1.5 kOhm [4308M- 101-152LF]	1.5 kOhm [4310R- 102-152]	1.5 kOhm [4607X- 101-152LF]
1.5 kOhm [4116R- 1-152]	1.5 kOhm [4308R- 101-152]	1.5 kOhm [4310R- 102-152LF]	1.5 kOhm [4608H- 102-152LF]
1.5 kOhm [4116R- 1-152LF]	1.5 kOhm [4308R- 101-152LF]	1.5 kOhm [4416P- 2-152]	1.5 kOhm [4608M- 102-152LF]

Multisim 14.1 Base Edition Components

1.5 kOhm [4608X-101-152LF]	1.5 kOhm [4614X-102-152LF]	1.5 kOhm [4820P-1-152]	1.5 kOhm [CR0201-JW-152GLF]
1.5 kOhm [4608X-102-152LF]	1.5 kOhm [4814P-1-152LF]	1.5 kOhm [4820P-2-152]	1.5 kOhm [CR0402-FX-1501GLF]
1.5 kOhm [4608X-AP1-152LF]	1.5 kOhm [4814P-2-152]	1.5 kOhm [4820P-T01-152]	1.5 kOhm [CR0402-JW-152GLF]
1.5 kOhm [4608X-AP2-152LF]	1.5 kOhm [4814P-2-152LF]	1.5 kOhm [4820P-T01-152LF]	1.5 kOhm [CR0603-FX-1501ELF]
1.5 kOhm [4609H-101-152LF]	1.5 kOhm [4814P-T01-152]	1.5 kOhm [4820P-T02-152]	1.5 kOhm [CR0603-JW-152ELF]
1.5 kOhm [4609X-101-152LF]	1.5 kOhm [4814P-T01-152LF]	1.5 kOhm [CAT10-152J4LF]	1.5 kOhm [CR0603-JW-152GLF]
1.5 kOhm [4609X-AP1-152LF]	1.5 kOhm [4814P-T02-152]	1.5 kOhm [CAT16-1501F4LF]	1.5 kOhm [CR0805-FX-1501ELF]
1.5 kOhm [4610H-101-152LF]	1.5 kOhm [4814P-T02-152LF]	1.5 kOhm [CAT16-152J4LF]	1.5 kOhm [CR0805-FX-1501GLF]
1.5 kOhm [4610H-102-152LF]	1.5 kOhm [4816P-1-152]	1.5 kOhm [CAT25-152JALF]	1.5 kOhm [CR0805-JW-152ELF]
1.5 kOhm [4610X-101-152LF]	1.5 kOhm [4816P-1-152LF]	1.5 kOhm [CAY10-152J4LF]	1.5 kOhm [CR0805-JW-152GLF]
1.5 kOhm [4610X-102-152LF]	1.5 kOhm [4816P-2-152]	1.5 kOhm [CAY16-1501F4LF]	1.5 kOhm [CR1206-FX-1501ELF]
1.5 kOhm [4610X-AP1-152LF]	1.5 kOhm [4816P-2-152LF]	1.5 kOhm [CAY16-152J2LF]	1.5 kOhm [CR1206-FX-1501GLF]
1.5 kOhm [4611X-101-152LF]	1.5 kOhm [4816P-T01-152LF]	1.5 kOhm [CAY16-152J4LF]	1.5 kOhm [CR1206-JW-152ELF]
1.5 kOhm [4612X-101-152LF]	1.5 kOhm [4816P-T02-152]	1.5 kOhm [CAY16-152J8LF]	1.5 kOhm [CR1206-JW-152GLF]
1.5 kOhm [4613X-101-152LF]	1.5 kOhm [4816P-T02-152LF]	1.5 kOhm [CAY17-152JALF]	1.5 kOhm [CR2010-JW-152ELF]

Multisim 14.1 Base Edition Components

1.5 kOhm [CR2512-FX-1501ELF]	1.5 kOhm [CRT0805-BY-1501ELF]	1.5 mF [T530X158M003AT E008]	1.5 mH [SRE6603-152M]
1.5 kOhm [CR2512-JW-152ELF]	1.5 kOhm [PWR220T-35-1501J]	1.5 mF [T530X158M2R5AT E005]	1.5 mH [SRR0906-152YL]
1.5 kOhm [CRM1206-FX-1501ELF]	1.5 kOhm [PWR221T-30-1501F]	1.5 mF [TAJE158K002RNJ]	1.5 mH [SRR0908-152YL]
1.5 kOhm [CRM2512-FX-1501ELF]	1.5 kOhm [PWR2615W1501J]	1.5 mF [TPME158K002R00 12]	1.5 mH [SRR1005-152K]
1.5 kOhm [CRM2512-JW-152ELF]	1.5 kOhm [PWR2615W1501JE]]	1.5 mF [TPME158K002R00 15]	1.5 mH [SRR1206-152KL]
1.5 kOhm [CRT0402-BW-1501GLF]	1.5 kOhm [PWR263S-35-1501F]	1.5 mF [TPME158K002R00 18]	1.5 mH [SRR1208-152KL]
1.5 kOhm [CRT0402-BY-1501GLF]	1.5 kOhm [PWR4525W1501J]	1.5 mF [TPME158K004R00 18]	1.5 mH [SRR6603-152ML]
1.5 kOhm [CRT0603-BY-1501ELF]	1.5 kOhm [PWR4525W1501JE]]	1.5 mF [TRME158K002R00 18]	1.5 MOhm [4606X-102-155LF]
1.5 kOhm [CRT0603-DY-1501ELF]	1.5 kOhm [PWR6327W1501J]	1.5 mH [SDR0503-152JL]	1.5 MOhm [CAT25-155JALF]
1.5 kOhm [CRT0603-FX-1501ELF]	1.5 kOhm [PWR6327W1501JE]]	1.5 mH [SDR0805-152KL]	1.5 MOhm [CR0402-FX-1504GLF]
1.5 kOhm [CRT0603-PV-1501ELF]	1.5 mF [2R5TPE1500MC]	1.5 mH [SDR0906-152KL]	1.5 MOhm [CR0402-JW-155GLF]
1.5 kOhm [CRT0805-BX-1501ELF]	1.5 mF [2R5TPE1500MF]	1.5 mH [SDR1005-152KL]	1.5 MOhm [CR0603-FX-1504ELF]
		1.5 mH [SDR1006-152KL]	1.5 MOhm [CR0603-JW-155ELF]

Multisim 14.1 Base Edition Components

1.5 MOhm [CR0805-FX- 1504ELF]	1.5 nF [C0402C152K8RACT U]	1.5 nF [C0805C152K1RACT U]	1.5 nF [C1206C152K2RACT U]
1.5 MOhm [CR0805-JW- 155ELF]	1.5 nF [C0603C152K1HACT U]	1.5 nF [C0805C152K2RACT U]	1.5 nF [C1206C152K5GACT U]
1.5 MOhm [CR1206-FW- 1504ELF]	1.5 nF [C0603C152K1RACT U]	1.5 nF [C0805C152K3RACT U]	1.5 nF [C1206C152K5RACT U]
1.5 MOhm [CR1206-JW- 155ELF]	1.5 nF [C0603C152K2RACT U]	1.5 nF [C0805C152K4GACT U]	1.5 nF [C1210C152K1GACT U]
1.5 MOhm [CRT0805-DZ- 1504ELF]	1.5 nF [C0603C152K3HACT U]	1.5 nF [C0805C152K4RACT U]	1.5 nF [C1210C152K5GACT U]
1.5 mOhm [CST0612-FC- R0015E]	1.5 nF [C0603C152K3RACT U]	1.5 nF [C0805C152K5GACT U]	1.5 nF [C1210C152KBGAC TU]
1.5 nF [C0402C152K3HACT U]	1.5 nF [C0603C152K4RACT U]	1.5 nF [C0805C152K5RACT U]	1.5 nF [C1812C152K2GACT U]
1.5 nF [C0402C152K3RACT U]	1.5 nF [C0603C152K5HACT U]	1.5 nF [C0805C152KARACT U]	1.5 nF [C1812C152KBGAC TU]
1.5 nF [C0402C152K4RACT U]	1.5 nF [C0603C152K5RACT U]	1.5 nF [C1206C152K1GACT U]	1.5 nF [C1825C152KBGAC TU]
1.5 nF [C0402C152K5HACT U]	1.5 nF [C0603C152K8RACT U]	1.5 nF [C1206C152K1RACT U]	1.5 nF [C2220C152KBGAC TU]
1.5 nF [C0402C152K5RACT U]	1.5 nF [C0805C152K1GACT U]	1.5 nF [C1206C152K2GACT U]	1.5 nF [C2225C152KBGAC TU]

Multisim 14.1 Base Edition Components

1.5 nF [CDR04BP152BKSM]	1.5 nF [MMC5.7152K100J 31TR12]	1.5 nF [SPC7.3152K630K31 TR12]	1.5 Ohm [CRL2512- FW-1R50ELF]
1.5 nF [GMC5.7152K100J3 1TR12]	1.5 nF [MMC5.7152K250J 31TR12]	1.5 Ohm [CR0402- J/-1R5GLF]	1.5 Ohm [CRM0805-JW- 1R5ELF]
1.5 nF [GMC5.7152K50J31 TR12]	1.5 nF [MMC5.7152K50J3 1TR12]	1.5 Ohm [CR0603- J/-1R5ELF]	1.5 Ohm [CRM1206-FX- 1R50ELF]
1.5 nF [GMC5.7153K250J3 3TR12]	1.5 nF [MMC7.3152K100K 31TR12]	1.5 Ohm [CR0805- J/-1R5ELF]	1.5 Ohm [CRM2010-FX- 1R50ELF]
1.5 nF [GMC7.3152K100K3 1TR12]	1.5 nF [MMC7.3152K250K 31TR12]	1.5 Ohm [CR1206- J/-1R5ELF]	1.5 Ohm [CRM2512-JW- 1R5ELF]
1.5 nF [GMC7.3152K400K3 1TR12]	1.5 nF [MMC7.3152K400K 31TR12]	1.5 Ohm [CR2512- J/-1R5ELF]	1.5 Ohm [PWR163S-25- 1R50F]
1.5 nF [GMC7.3153K100K3 1TR12]	1.5 nF [MMC7.3152K50K3 1TR12]	1.5 Ohm [CRL0603- FW-1R50ELF]	1.5 Ohm [PWR163S-25- 1R50FE]
1.5 nF [GMC7.3153K400K3 7TR12]	1.5 nF [MMC7.3152K63K3 1TR12]	1.5 Ohm [CRL0805- FW-1R50ELF]	1.5 Ohm [PWR163S-25- 1R50J]
1.5 nF [GPC7.3152K160K3 1TR12]	1.5 nF [SPC7.3152K100K31 TR12]	1.5 Ohm [CRL0805- JW-1R50ELF]	1.5 Ohm [PWR220T-20- 1R50F]
1.5 nF [GPC7.3152K630K3 1TR12]	1.5 nF [SPC7.3152K250K31 TR12]	1.5 Ohm [CRL1206- FW-1R50ELF]	1.5 Ohm [PWR220T-20- 1R50J]
1.5 nF [GPC7.3152K63K31 TR12]	1.5 nF [SPC7.3152K400K31 TR12]	1.5 Ohm [CRL2010- FW-1R50ELF]	1.5 Ohm [PWR220T-35- 1R50J]

Multisim 14.1 Base Edition Components

1.5 Ohm [PWR221T-30-1R50F]	1.5 Ohm [PWR4525W1R50JE]	1.5 uF [C1206C155K4RACTU]	1.5 uF [C2225C155K5RACTU]
1.5 Ohm [PWR2615W1R50F]	1.5 Ohm [PWR6327N1R50F]	1.5 uF [C1206C155K8PACTU]	1.5 uF [C2225C155M5UAC TU]
1.5 Ohm [PWR2615W1R50FE]	1.5 Ohm [PWR6327W1R50F]	1.5 uF [C1206C155K8RACTU]	1.5 uF [MDC10155K100A52P3TUBE]
1.5 Ohm [PWR2615W1R50J]	1.5 uF [O5086D155KAT2A]	1.5 uF [C1206C155K9RACTU]	1.5 uF [MDC10155K250A58P7TUBE]
1.5 Ohm [PWR263S-20-1R50F]	1.5 uF [C0805C155K4PACTU]	1.5 uF [C1210C155K3PACTU]	1.5 uF [MDC10155K250A58P8TUBE]
1.5 Ohm [PWR263S-20-1R50J]	1.5 uF [C0805C155K4RACTU]	1.5 uF [C1210C155K3RACTU]	1.5 uF [MDC10155K50A52P3TUBE]
1.5 Ohm [PWR263S-20-1R50JE]	1.5 uF [C0805C155K8PACTU]	1.5 uF [C1210C155K4RACTU]	1.5 uF [MDC15155K100B53P3TUBE]
1.5 Ohm [PWR263S-35-1R50F]	1.5 uF [C0805C155K8RACTU]	1.5 uF [C1210F155K4RACTU]	1.5 uF [MDC15155K50B53P3TUBE]
1.5 Ohm [PWR263S-35-1R50J]	1.5 uF [C0805C155K9PACTU]	1.5 uF [C1825C155K5RACTU]	1.5 uF [MDK10155K50A52P3TUBE]
1.5 Ohm [PWR3014WA1R50JE]	1.5 uF [C0805C155K9RACTU]	1.5 uF [C1825C155M5UAC TU]	1.5 uF [MDS10155K100A52P3TUBE]
1.5 Ohm [PWR4525W1R50F]	1.5 uF [C1206C155K3RACTU]	1.5 uF [C2220C155K5RACTU]	1.5 uF [MDS10155K50A52P3TUBE]
1.5 Ohm [PWR4525W1R50J]	1.5 uF [C1206C155K4PACTU]		

Multisim 14.1 Base Edition Components

1.5 uF [MDS15155K100B5 3P3TUBE]	1.5 uF [T494A155M016AT]	1.5 uF [TAJA155K025RNJ]	1.5 uF [TAJT155K020RNJ]
1.5 uF [T419A155M015AH 4250]	1.5 uF [T494A155M025AT]	1.5 uF [TAJA155K035RNJ]	1.5 uF [TAJT155K025RNJ]
1.5 uF [T489C155M050AT E1K5]	1.5 uF [T494B155M025AT]	1.5 uF [TAJB155K025RNJ]	1.5 uF [TAJT155K035RNJ]
1.5 uF [T491A155M010AT]	1.5 uF [T494B155M035AT]	1.5 uF [TAJB155K035RNJ]	1.5 uF [THJA155K020RJJ]
1.5 uF [T491A155M016AT]	1.5 uF [T494C155M035AT]	1.5 uF [TAJC155K035RNJ]	1.5 uF [THJC155K035RJJ]
1.5 uF [T491A155M020AT]	1.5 uF [T494C155M050AT]	1.5 uF [TAJC155K050RNJ]	1.5 uF [TPSA155K025R300 0]
1.5 uF [T491A155M025AT]	1.5 uF [T494D155M050AT]	1.5 uF [TAJD155K050RNJ]	1.5 uF [TPSB155K025R180 0]
1.5 uF [T491A155M025AT]	1.5 uF [T494S155M020AT]	1.5 uF [TAJP155K025RNJ]	1.5 uF [TPSB155K035R250 0]
1.5 uF [T491B155M025AT]	1.5 uF [T498C155M035AT E3K3]	1.5 uF [TAJR155K006RNJ]	1.5 uF [TPSC155K050R150 0]
1.5 uF [T491B155M035AT]	1.5 uF [TACL155K004RTA]	1.5 uF [TAJR155K010RNJ]	1.5 uF [TPSC155K050R200 0]
1.5 uF [T491C155M035AT]	1.5 uF [TACL155K006RTA]	1.5 uF [TAJR155K016RNJ]	1.5 uF [TPSC155K050R200 0]
1.5 uF [T491C155M050AT]	1.5 uF [TACL155K010RTA]	1.5 uF [TAJS155K006RNJ]	1.5 uF [TRJA155K025RRJ]
1.5 uF [T491D155M050AT]	1.5 uF [TAJA155K010RNJ]	1.5 uF [TAJS155K010RNJ]	1.5 uF [TRJA155K035RRJ]
1.5 uF [T491S155M020AT]	1.5 uF [TAJA155K016RNJ]	1.5 uF [TAJS155K016RNJ]	1.5 uH [SDE0604A- 1R5M]
1.5 uF [T494A155M010AT]	1.5 uF [TAJA155K020RNJ]		

Multisim 14.1 Base Edition Components

1.5 uH [SDE0805A-1R5M]	1.5 uH [SRN3010-1R5Y]	1.5 uH [SRP1270-1R5M]	1.5 uH [SRR0908-1R5ML]
1.5 uH [SDE1006A-1R5M]	1.5 uH [SRN3015-1R5Y]	1.5 uH [SRP1770TA-1R5M]	1.5 uH [SRR1005-1R5M]
1.5 uH [SDR0302-1R5ML]	1.5 uH [SRN4012T-1R5M]	1.5 uH [SRP4012-1R5M]	1.5 uH [SRR1240-1R5Y]
1.5 uH [SDR0603-1R5ML]	1.5 uH [SRN4018-1R5Y]	1.5 uH [SRP4012TA-1R5M]	1.5 uH [SRR1260-1R5Y]
1.5 uH [SDR0604-1R5ML]	1.5 uH [SRN5020-1R5Y]	1.5 uH [SRP4020-1R5M]	1.5 uH [SRR1260A-1R5Y]
1.5 uH [SDR0805-1R5ML]	1.5 uH [SRN5040-1R5Y]	1.5 uH [SRP4020TA-1R5M]	1.5 uH [SRR3011-1R5YL]
1.5 uH [SDR1005-1R5ML]	1.5 uH [SRN6028-1R5Y]	1.5 uH [SRP5015TA-1R5M]	1.5 uH [SRR4011-1R5YL]
1.5 uH [SDR1006-1R5ML]	1.5 uH [SRN8040-1R5Y]	1.5 uH [SRP5030T-1R5M]	1.5 uH [SRR6028-1R5Y]
1.5 uH [SDR1307-1R5ML]	1.5 uH [SRP1038A-1R5M]	1.5 uH [SRP5030TA-1R5M]	1.5 uH [SRR6603-1R5ML]
1.5 uH [SDR1307A-1R5M]	1.5 uH [SRP1040-1R5M]	1.5 uH [SRP6540-1R5M]	1.5 uH [SRU1028-1R5Y]
1.5 uH [SDR6603-1R5M]	1.5 uH [SRP1206-1R3Z]	1.5 uH [SRP7028A-1R5M]	1.5 uH [SRU1028A-1R5Y]
1.5 uH [SDR7030-1R5M]	1.5 uH [SRP1235-1R5M]	1.5 uH [SRP7030-1R5FM]	1.5 uH [SRU1038-1R5Y]
1.5 uH [SDR7045-1R5M]	1.5 uH [SRP1245A-1R5M]	1.5 uH [SRP7050TA-1R5M]	1.5 uH [SRU1038A-1R5Y]
1.5 uH [SRN2012-1R5M]	1.5 uH [SRP1250-1R5M]	1.5 uH [SRR0603-1R5ML]	1.5 uH [SRU1048-1R5Y]
1.5 uH [SRN2512-1R5M]	1.5 uH [SRP1265A-1R5M]	1.5 uH [SRR0604-1R5ML]	1.5 uH [SRU1048A-1R5Y]

Multisim 14.1 Base Edition Components

1.5 uH [SRU3011-1R5Y]	1.58 kOhm [CR1206-FX-1581ELF]	1.5KE39CA-E3/54	1.5SMC6.8A/57T
1.5 uH [SRU3014-1R5Y]	1.58 kOhm [CRT0402-BY-1581GLF]	1.5KE47A-E3/54	1.5SMC6.8AT3G
1.5 uH [SRU5011-1R5Y]	1.58 kOhm [CRT0402-BY-1581GLF]	1.5KE47AG	1.5SMC6.8CA-E3/57T
1.5 uH [SRU5018-1R5Y]	1.58 kOhm [CRT0805-BY-1581ELF]	1.5KE47ARL4G	1.5SMC62AT3G
1.54 kOhm [CR0402-FX-1541GLF]	1.5KA27AHE3/54	1.5KE51CA-E3/54	1.5SMC75CA-E3/57T
1.54 kOhm [CR0603-FX-1541ELF]	1.5KE100A-E3/54	1.5KE75ARL4G	1.5SMC91AT3G
1.54 kOhm [CR0805-FX-1541ELF]	1.5KE100CA-E3/54	1.5KE91A-E3/54	1.6 kOhm [4116R-2-162]
1.54 kOhm [CR1206-FX-1541ELF]	1.5KE110CA-E3/54	1.5KE91ARL4G	1.6 kOhm [4308H-101-162]
1.54 kOhm [CRT0805-BY-1541ELF]	1.5KE12A-E3/54	1.5SMC12AT3G	1.6 kOhm [4308M-102-162]
1.54 kOhm [CR0402-FX-1541GLF]	1.5KE12CA-E3/54	1.5SMC13A-E3/57T	1.6 kOhm [4308M-102-162LF]
1.54 kOhm [CR1206-FX-1541ELF]	1.5KE130CA-E3/54	1.5SMC15AT3G	1.6 kOhm [4308M-102-162J4LF]
1.54 kOhm [CR0805-FX-1541ELF]	1.5KE160CA-E3/54	1.5SMC15CA-E3/57T	1.6 kOhm [CAT16-162J4LF]
1.54 kOhm [CRT0805-BY-1541ELF]	1.5KE180A-E3/54	1.5SMC180A-E3/57T	1.6 kOhm [CAY16-162J4LF]
1.58 kOhm [CR0402-FX-1581GLF]	1.5KE18A-E3/54	1.5SMC18CA-E3/57T	1.6 kOhm [CR0402-FX-1601GLF]
1.58 kOhm [CR0603-FX-1581ELF]	1.5KE200A-E3/54	1.5SMC18AT3G	1.6 kOhm [CR0603-FX-1601ELF]
1.58 kOhm [CR0805-FX-1581ELF]	1.5KE200CA-E3/54	1.5SMC20AT3G	1.6 kOhm [CR0603-JW-162ELF]
1.58 kOhm [CR1206-FX-1581ELF]	1.5KE20A-E3/51	1.5SMC24AT3G	1.6 kOhm [CR0805-FX-1601ELF]
1.58 kOhm [CR0402-FX-1541GLF]	1.5KE220CA-E3/54	1.5SMC33AT3G	1.6 kOhm [CR0805-JW-162ELF]
1.58 kOhm [CR0603-FX-1581ELF]	1.5KE24CA-E3/54	1.5SMC39A-E3/57T	
1.58 kOhm [CR0805-FX-1581ELF]	1.5KE36A-E3/54	1.5SMC39AT3G	
	1.5KE36CA-E3/54	1.5SMC43AT3G	
	1.5KE39ARL4G	1.5SMC540A-E3/57T	

Multisim 14.1 Base Edition Components

1.6 kOhm [CR1206-FX-1601ELF]	1.6 nF [C1812C162KBGAC TU]	1.6 Ohm [CRL2010-FW-1R60ELF]	1.65 kOhm [CR0805-FX-1651ELF]
1.6 kOhm [CR1206-JW-162ELF]	1.6 nF [C1825C162KBGAC TU]	1.6 Ohm [CRL2010-JW-1R60ELF]	1.65 kOhm [CR1206-FX-1651ELF]
1.6 MOhm [CR0603-JW-165ELF]	1.6 nF [C2220C162KBGAC TU]	1.6 Ohm [CRL2512-FW-1R60ELF]	1.65 kOhm [CRT0603-PW-1651ELF]
1.6 MOhm [CR0805-JW-165ELF]	1.6 nF [C2225C162KBGAC TU]	1.62 kOhm [CR0402-FX-1621GLF]	1.65 kOhm [CRT1206-BY-1651ELF]
1.6 MOhm [CR1206-FW-1604ELF]	1.6 Ohm [CR0402-J/-1R6GLF]	1.62 kOhm [CR0603-FX-1621ELF]	1.69 kOhm [CAT16-1691F4LF]
1.6 MOhm [CR1206-JW-165ELF]	1.6 Ohm [CR0603-J/-1R6ELF]	1.62 kOhm [CR0805-FX-1621ELF]	1.69 kOhm [CR0402-FX-1691GLF]
1.6 nF [C0603C162K1HACT U]	1.6 Ohm [CR0805-J/-1R6ELF]	1.62 kOhm [CR1206-FX-1621ELF]	1.69 kOhm [CR0603-FX-1691ELF]
1.6 nF [C0603C162K3HACT U]	1.6 Ohm [CRL0603-FW-1R60ELF]	1.62 kOhm [CR2010-FX-1621ELF]	1.69 kOhm [CR0805-FX-1691ELF]
1.6 nF [C0603C162K5HACT U]	1.6 Ohm [CRL0603-JW-1R60ELF]	1.62 kOhm [CRT0402-FZ-1621GLF]	1.69 kOhm [CR1206-FX-1691ELF]
1.6 nF [C0805C162K4GACT U]	1.6 Ohm [CRL0805-FW-1R60ELF]	1.65 kOhm [CR0402-FX-1651GLF]	1.69 kOhm [CRT0402-BW-1691GLF]
1.6 nF [C1206C162K5GACT U]	1.6 Ohm [CRL1206-FW-1R60ELF]	1.65 kOhm [CR0603-FX-1651ELF]	
1.6 nF [C1210C162KBGAC TU]	1.6 Ohm [CRL1206-JW-1R60ELF]		

Multisim 14.1 Base Edition Components

1.69 kOhm [CRT1206-BY- 1691ELF]	1.78 kOhm [CR0805-FX- 1781ELF]	1.8 kOhm [4306M- 102-182]	1.8 kOhm [4310H- 102-182LF]
1.7 uH [SRP1040- 1R7M]	1.78 kOhm [CR1206-FX- 1781ELF]	1.8 kOhm [4306M- 102-182LF]	1.8 kOhm [4310M- 101-182]
1.74 kOhm [CR0402-FX- 1741GLF]	1.78 kOhm [CRT0402-FZ- 1781GLF]	1.8 kOhm [4306R- 101-182]	1.8 kOhm [4310M- 102-182]
1.74 kOhm [CR0603-FX- 1741ELF]	1.78 kOhm [CRT1206-DX- 1781ELF]	1.8 kOhm [4306R- 102-182]	1.8 kOhm [4310R- 101-182]
1.74 kOhm [CR0805-FX- 1741ELF]	1.78 MOhm [CR1206-FW- 1784ELF]	1.8 kOhm [4306R- 102-182LF]	1.8 kOhm [4310R- 101-182LF]
1.74 kOhm [CR1206-FX- 1741ELF]	1.8 kOhm [4114R- 1-182]	1.8 kOhm [4308M- 102-182]	1.8 kOhm [4310R- 102-182]
1.74 kOhm [CRT0603-BY- 1741ELF]	1.8 kOhm [4114R- 1-182LF]	1.8 kOhm [4308M- 102-182LF]	1.8 kOhm [4310R- 102-182LF]
1.74 MOhm [CR0805-FX- 1744ELF]	1.8 kOhm [4114R- 2-182]	1.8 kOhm [4308R- 101-182]	1.8 kOhm [4420P- T02-182]
1.74 Ohm [CRT1206-DZ- 1R74ELF]	1.8 kOhm [4114R- 2-182LF]	1.8 kOhm [4308R- 101-182LF]	1.8 kOhm [4604X- 102-182LF]
1.74 Ohm [CRT1206-DZ- 1R74ELF]	1.8 kOhm [4114R- 2-182LF]	1.8 kOhm [4308R- 102-182]	1.8 kOhm [4605X- 101-182LF]
1.78 kOhm [CR0402-FX- 1781GLF]	1.8 kOhm [4116R- 1-182]	1.8 kOhm [4308R- 102-182LF]	1.8 kOhm [4606H- 101-182LF]
1.78 kOhm [CR0603-FX- 1781ELF]	1.8 kOhm [4116R- 1-182LF]	1.8 kOhm [4309R- 101-182]	1.8 kOhm [4606X- 101-182LF]
	1.8 kOhm [4116R- 2-182]	1.8 kOhm [4309R- 101-182LF]	1.8 kOhm [4606X- 102-182LF]
	1.8 kOhm [4116R- 2-182LF]	1.8 kOhm [4310H- 102-182]	1.8 kOhm [4607X- 101-182LF]

Multisim 14.1 Base Edition Components

1.8 kOhm [4608H-102-182LF]	1.8 kOhm [4816P-T01-182]	1.8 kOhm [CR0603-FX-1801ELF]	1.8 kOhm [CRM2512-JW-182ELF]
1.8 kOhm [4608M-102-182LF]	1.8 kOhm [4816P-T01-182LF]	1.8 kOhm [CR0603-FX-1801GLF]	1.8 kOhm [CRT0603-BX-1801ELF]
1.8 kOhm [4608X-101-182LF]	1.8 kOhm [4816P-T02-182]	1.8 kOhm [CR0603-JW-182ELF]	1.8 kOhm [CRT0603-BY-1801ELF]
1.8 kOhm [4608X-102-182LF]	1.8 kOhm [4816P-T02-182LF]	1.8 kOhm [CR0805-FX-1801ELF]	1.8 kOhm [CRT0805-BY-1801ELF]
1.8 kOhm [4608X-AP1-182LF]	1.8 kOhm [4820P-2-182]	1.8 kOhm [CR0805-FX-1801GLF]	1.8 kOhm [CRT0805-DY-1801ELF]
1.8 kOhm [4608X-AP2-182LF]	1.8 kOhm [CAT16-1801F4LF]	1.8 kOhm [CR0805-JW-182ELF]	1.8 kOhm [CRT0805-DY-1801ELF]
1.8 kOhm [4609X-101-182LF]	1.8 kOhm [CAT16-182J4LF]	1.8 kOhm [CR0805-JW-182GLF]	1.8 kOhm [CRT0805-FX-1801ELF]
1.8 kOhm [4610H-101-182LF]	1.8 kOhm [CAT25-182JALF]	1.8 kOhm [CR1206-FX-1801ELF]	1.8 mH [SDR0503-182JL]
1.8 kOhm [4610X-101-182LF]	1.8 kOhm [CAY10-182J4LF]	1.8 kOhm [CR1206-JW-182ELF]	1.8 mH [SDR0805-182KL]
1.8 kOhm [4610X-102-182LF]	1.8 kOhm [CAY16-1801F4LF]	1.8 kOhm [CR1206-JW-182GLF]	1.8 mH [SDR0906-182KL]
1.8 kOhm [4612X-102-182LF]	1.8 kOhm [CAY16-182J4LF]	1.8 kOhm [CR2512-JW-182ELF]	1.8 mH [SDR1006-182KL]
1.8 kOhm [4816P-1-182]	1.8 kOhm [CAY16-182J8LF]	1.8 kOhm [CRM1206-FX-1801ELF]	1.8 mH [SRR0906-182YL]
1.8 kOhm [4816P-1-182LF]	1.8 kOhm [CAY17-182JALF]	1.8 kOhm [CRM1206-JW-182ELF]	1.8 mH [SRR1005-182K]
1.8 kOhm [4816P-2-182]	1.8 kOhm [CR0402-FX-1801GLF]	1.8 kOhm [CRM2010-JW-182ELF]	1.8 mH [SRR1208-182KL]
1.8 kOhm [4816P-2-182LF]	1.8 kOhm [CR0402-JW-182GLF]		

Multisim 14.1 Base Edition Components

1.8 MOhm [4310R-101-185]	1.8 nF [C0603C182K3HACT U]	1.8 nF [C1206C182K1GACT U]	1.8 nF [C2220C182KBGAC TU]
1.8 MOhm [CAT25-185JALF]	1.8 nF [C0603C182K3RACT U]	1.8 nF [C1206C182K1RACT U]	1.8 nF [C2225C182KBGAC TU]
1.8 MOhm [CHV0805-FX-1804ELF]	1.8 nF [C0603C182K5HACT U]	1.8 nF [C1206C182K2GACT U]	1.8 nF [GMC5.7182K100J3 1TR12]
1.8 MOhm [CR0603-JW-185ELF]	1.8 nF [C0603C182K5RACT U]	1.8 nF [C1206C182K5GACT U]	1.8 nF [GMC5.7182K50J31 TR12]
1.8 MOhm [CR0805-FX-1804ELF]	1.8 nF [C0805C182K1GACT U]	1.8 nF [C1206C182K5RACT U]	1.8 nF [GMC5.7183K250J3 3TR12]
1.8 MOhm [CR0805-JW-185ELF]	1.8 nF [C0805C182K1RACT U]	1.8 nF [C1210C182K1GACT U]	1.8 nF [GMC7.3182K100K3 1TR12]
1.8 MOhm [CR1206-FW-1804ELF]	1.8 nF [C0805C182K2RACT U]	1.8 nF [C1210C182K2GACT U]	1.8 nF [GMC7.3182K400K3 1TR12]
1.8 MOhm [CR1206-JW-185ELF]	1.8 nF [C0805C182K4RACT U]	1.8 nF [C1210C182K5GACT U]	1.8 nF [GMC7.3183K100K3 1TR12]
1.8 nF [C0402C182K3RACT U]	1.8 nF [C0805C182K5GACT U]	1.8 nF [C1210C182KBGAC TU]	1.8 nF [GMC7.3183K250K3 3TR12]
1.8 nF [C0402C182K5RACT U]	1.8 nF [C0805C182K5RACT U]	1.8 nF [C1812C182KBGAC TU]	1.8 nF [MMC5.7182K100J 31TR12]
1.8 nF [C0603C182K1HACT U]	1.8 nF [C0805C182KARACT U]	1.8 nF [C1825C182KBGAC TU]	1.8 nF [MMC5.7182K250J 31TR12]
1.8 nF [C0603C182K1RACT U]			

Multisim 14.1 Base Edition Components

1.8 nF [MMC5.7182K50J3 1TR12]	1.8 Ohm [CRL0805- JW-1R80ELF]	1.8 uF [C0805C185K8PACT U]	1.8 uF [C2220C185K5RACT U]
1.8 nF [MMC7.3182K100K 31TR12]	1.8 Ohm [CRL1206- FW-1R80ELF]	1.8 uF [C0805C185K8RACT U]	1.8 uF [C2225C185K5RACT U]
1.8 nF [MMC7.3182K250K 31TR12]	1.8 Ohm [CRL2010- FW-1R80ELF]	1.8 uF [C0805C185K9PACT U]	1.8 uF [C2225C185M5UAC TU]
1.8 nF [MMC7.3182K400K 31TR12]	1.8 Ohm [CRL2010- JW-1R80ELF]	1.8 uF [C0805C185K9RACT U]	1.8 uF [MDC10185K100A5 2P3TUBE]
1.8 nF [MMC7.3182K50K3 1TR12]	1.8 Ohm [CRL2512- FW-1R80ELF]	1.8 uF [C1206C185K3PACT U]	1.8 uF [MDC10185K50A52 P3TUBE]
1.8 nF [MMC7.3182K63K3 1TR12]	1.8 Ohm [CRM1206-FX- 1R80ELF]	1.8 uF [C1206C185K4RACT U]	1.8 uF [MDC15185K100B5 3P3TUBE]
1.8 Ohm [CR0402- J/-1R8GLF]	1.8 Ohm [CRM2512-JW- 1R8ELF]	1.8 uF [C1206C185K8RACT U]	1.8 uF [MDC15185K50B53 P3TUBE]
1.8 Ohm [CR0603- J/-1R8ELF]	1.8 Ohm [PWR2615W1R80J]	1.8 uF [C1210C185K3PACT U]	1.8 uF [MDK15185K100B5 3P3TUBE]
1.8 Ohm [CR0805- J/-1R8ELF]	1.8 Ohm [PWR263S-35- 1R80J]	1.8 uF [C1210C185K3RACT U]	1.8 uF [MDK15185K50B53 P3TUBE]
1.8 Ohm [CR1206- J/-1R8ELF]	1.8 Ohm [PWR5322W1R80JE]	1.8 uF [C1210F185K4RACT U]	1.8 uF [MMC12.7185K63B 31TR24]
1.8 Ohm [CRL0603- FW-1R80ELF]	1.8 uF [C0805C185K4PACT U]	1.8 uF [C1825C185K5RACT U]	1.8 uH [SDR0302- 1R8ML]
1.8 Ohm [CRL0603- JW-1R80ELF]			1.8 uH [SDR0403- 1R8ML]
1.8 Ohm [CRL0805- FW-1R80ELF]			

Multisim 14.1 Base Edition Components

1.8 uH [SDR0703-1R8ML]	1.82 kOhm [CR0402-FX-1821GLF]	1.9 kOhm [4416P-2-192]	1.96 kOhm [CRT0603-CY-1961ELF]
1.8 uH [SRN6045-1R8Y]	1.82 kOhm [CR0603-FX-1821ELF]	1.9 kOhm [4420P-1-192]	1_AMP
1.8 uH [SRP1235-1R8M]	1.82 kOhm [CR0805-FX-1821ELF]	1.91 kOhm [CR0402-FX-1911GLF]	10 kOhm [4108R-1-103]
1.8 uH [SRP1250-1R8M]	1.82 kOhm [CR1206-FX-1821ELF]	1.91 kOhm [CR0603-FX-1911ELF]	10 kOhm [4108R-1-103LF]
1.8 uH [SRP1270-1R8M]	1.82 kOhm [CR2512-FX-1821ELF]	1.91 kOhm [CR0805-FX-1911ELF]	10 kOhm [4108R-2-103]
1.8 uH [SRP7028A-1R8M]	1.82 kOhm [CR2512-FX-1821ELF]	1.91 kOhm [CR1206-FX-1911ELF]	10 kOhm [4108R-2-103LF]
1.8 uH [SRP7050TA-1R8M]	1.82 Ohm [PWR163S-25-1R82FE]	1.91 kOhm [CRM2512-FX-1911ELF]	10 kOhm [4114R-1-103]
1.8 uH [SRR1003-1R8M]	1.87 kOhm [CR0402-FX-1871GLF]	1.91 kOhm [CAT16-1961F4LF]	10 kOhm [4114R-1-103LF]
1.8 uH [SRR1210-1R8Y]	1.87 kOhm [CR0603-FX-1871ELF]	1.96 kOhm [CR0402-FX-1961GLF]	10 kOhm [4114R-2-103]
1.8 uH [SRR1210A-1R8Y]	1.87 kOhm [CR0805-FX-1871ELF]	1.96 kOhm [CR0603-FX-1961ELF]	10 kOhm [4114R-2-103LF]
1.8 uH [SRR4018-1R8Y]	1.87 kOhm [CR1206-FX-1871ELF]	1.96 kOhm [CR0805-FX-1961ELF]	10 kOhm [4116R-1-103]
1.8 uH [SRR4028-1R8Y]	1.87 kOhm [CRT1206-FZ-1871ELF]		10 kOhm [4116R-1-103LF]
1.8 uH [SRR5018-1R8Y]			10 kOhm [4116R-2-103]
1.8 uH [SRU5016-1R8Y]			10 kOhm [4116R-2-103LF]
1.8 uH [SRU6018-1R8Y]			10 kOhm [4304M-101-103]

Multisim 14.1 Base Edition Components

10 kOhm [4304M-101-103LF]	10 kOhm [4308H-102-103]	10 kOhm [4310H-102-103LF]	10 kOhm [4416P-T01-103]
10 kOhm [4304M-102-103]	10 kOhm [4308H-102-103LF]	10 kOhm [4310M-101-103]	10 kOhm [4416P-T02-103]
10 kOhm [4304M-102-103LF]	10 kOhm [4308M-101-103]	10 kOhm [4310M-101-103LF]	10 kOhm [4416P-T02-103LF]
10 kOhm [4306H-101-103]	10 kOhm [4308M-101-103LF]	10 kOhm [4310M-102-103]	10 kOhm [4420P-1-103]
10 kOhm [4306H-101-103LF]	10 kOhm [4308M-102-103]	10 kOhm [4310M-102-103LF]	10 kOhm [4420P-1-103LF]
10 kOhm [4306M-101-103]	10 kOhm [4308M-102-103LF]	10 kOhm [4310R-101-103]	10 kOhm [4420P-2-103]
10 kOhm [4306M-101-103LF]	10 kOhm [4308R-101-103]	10 kOhm [4310R-101-103LF]	10 kOhm [4420P-2-103LF]
10 kOhm [4306M-102-103]	10 kOhm [4308R-101-103LF]	10 kOhm [4310R-102-103]	10 kOhm [4420P-T01-103]
10 kOhm [4306M-102-103LF]	10 kOhm [4308R-102-103]	10 kOhm [4310R-102-103LF]	10 kOhm [4420P-T02-103]
10 kOhm [4306R-101-103]	10 kOhm [4308R-102-103LF]	10 kOhm [4311R-101-103]	10 kOhm [4420P-T02-103LF]
10 kOhm [4306R-101-103LF]	10 kOhm [4309R-101-103]	10 kOhm [4311R-101-103LF]	10 kOhm [4420P-T04-103]
10 kOhm [4306R-102-103]	10 kOhm [4309R-101-103LF]	10 kOhm [4416P-1-103]	10 kOhm [4604H-101-103LF]
10 kOhm [4306R-102-103LF]	10 kOhm [4310H-101-103]	10 kOhm [4416P-1-103LF]	10 kOhm [4604X-101-103LF]
10 kOhm [4308H-101-103]	10 kOhm [4310H-101-103LF]	10 kOhm [4416P-2-103]	10 kOhm [4604X-102-103LF]
10 kOhm [4308H-101-103LF]	10 kOhm [4310H-102-103]	10 kOhm [4416P-2-103LF]	10 kOhm [4604X-AP1-103LF]

Multisim 14.1 Base Edition Components

10 kOhm [4605H-101-103LF]	10 kOhm [4608H-102-103LF]	10 kOhm [4610X-101-103LF]	10 kOhm [4814P-2-103LF]
10 kOhm [4605M-101-103LF]	10 kOhm [4608M-101-103LF]	10 kOhm [4610X-102-103LF]	10 kOhm [4814P-T01-103]
10 kOhm [4605X-101-103LF]	10 kOhm [4608M-102-103LF]	10 kOhm [4610X-AP1-103LF]	10 kOhm [4814P-T01-103LF]
10 kOhm [4605X-AP1-103LF]	10 kOhm [4608X-101-103LF]	10 kOhm [4610X-AP2-103LF]	10 kOhm [4814P-T02-103]
10 kOhm [4606H-101-103LF]	10 kOhm [4608X-102-103LF]	10 kOhm [4611M-101-103LF]	10 kOhm [4814P-T02-103LF]
10 kOhm [4606H-102-103LF]	10 kOhm [4608X-AP1-103LF]	10 kOhm [4611X-101-103LF]	10 kOhm [4816P-1-103]
10 kOhm [4606M-101-103LF]	10 kOhm [4608X-AP2-103LF]	10 kOhm [4612H-101-103LF]	10 kOhm [4816P-1-103DLF]
10 kOhm [4606M-102-103LF]	10 kOhm [4609H-101-103LF]	10 kOhm [4612X-101-103LF]	10 kOhm [4816P-1-103F]
10 kOhm [4606X-101-103LF]	10 kOhm [4609M-101-103LF]	10 kOhm [4612X-102-103LF]	10 kOhm [4816P-1-103LF]
10 kOhm [4606X-102-103LF]	10 kOhm [4609X-101-103LF]	10 kOhm [4613X-101-103LF]	10 kOhm [4816P-2-103]
10 kOhm [4606X-AP1-103LF]	10 kOhm [4609X-AP1-103LF]	10 kOhm [4614X-101-103LF]	10 kOhm [4816P-2-103F]
10 kOhm [4606X-AP2-103LF]	10 kOhm [4610H-101-103LF]	10 kOhm [4614X-102-103LF]	10 kOhm [4816P-2-103LF]
10 kOhm [4607M-101-103LF]	10 kOhm [4610H-102-103LF]	10 kOhm [4814P-1-103]	10 kOhm [4816P-4-103]
10 kOhm [4607X-101-103LF]	10 kOhm [4610M-101-103LF]	10 kOhm [4814P-1-103LF]	10 kOhm [4816P-T01-103]
10 kOhm [4608H-101-103LF]	10 kOhm [4610M-102-103LF]	10 kOhm [4814P-2-103]	10 kOhm [4816P-T01-103LF]

Multisim 14.1 Base Edition Components

10 kOhm [4816P-T02-103]	10 kOhm [4820P-T02-103]	10 kOhm [CAY16-103J4LF]	10 kOhm [CR0805-JW-103GLF]
10 kOhm [4816P-T02-103LF]	10 kOhm [4820P-T02-103LF]	10 kOhm [CAY16-103J8LF]	10 kOhm [CR1206-FX-1002ELF]
10 kOhm [4818P-1-103]	10 kOhm [CAT10-103J4LF]	10 kOhm [CAY17-103JALF]	10 kOhm [CR1206-JW-103ELF]
10 kOhm [4818P-2-103]	10 kOhm [CAT16-1002F4LF]	10 kOhm [CR0201-FW-1002GLF]	10 kOhm [CR1206-JW-103GLF]
10 kOhm [4818P-2-103LF]	10 kOhm [CAT16-1002F8LF]	10 kOhm [CR0201-JW-103GLF]	10 kOhm [CR2010-FX-1002ELF]
10 kOhm [4818P-T01-103]	10 kOhm [CAT16-103J2LF]	10 kOhm [CR0402-FX-1002GLF]	10 kOhm [CR2010-JW-103ELF]
10 kOhm [4818P-T02-103]	10 kOhm [CAT16-103J4GLF]	10 kOhm [CR0402-JW-103GLF]	10 kOhm [CR2512-FX-1002ELF]
10 kOhm [4820P-1-103]	10 kOhm [CAT16-103J4LF]	10 kOhm [CR0603-FX-1002ELF]	10 kOhm [CR2512-JW-103ELF]
10 kOhm [4820P-1-103F]	10 kOhm [CAT16-103J8LF]	10 kOhm [CR0603-FX-1002GLF]	10 kOhm [CRM1206-FX-1002ELF]
10 kOhm [4820P-1-103LF]	10 kOhm [CAT25-103JALF]	10 kOhm [CR0603-FX-1002HLF]	10 kOhm [CRM1206-JW-103ELF]
10 kOhm [4820P-2-103]	10 kOhm [CAY10-103J2LF]	10 kOhm [CR0603-JW-103ELF]	10 kOhm [CRM2010-FX-1002ELF]
10 kOhm [4820P-2-103F]	10 kOhm [CAY10-103J4LF]	10 kOhm [CR0603-JW-103GLF]	10 kOhm [CRM2512-FX-1002ELF]
10 kOhm [4820P-2-103LF]	10 kOhm [CAY16-1002F4LF]	10 kOhm [CR0805-FX-1002ELF]	10 kOhm [CRM2512-JW-103ELF]
10 kOhm [4820P-T01-103]	10 kOhm [CAY16-103J2LF]	10 kOhm [CR0805-FX-1002GLF]	
10 kOhm [4820P-T01-103LF]	10 kOhm [CAY16-103J4GLF]	10 kOhm [CR0805-JW-103ELF]	

Multisim 14.1 Base Edition Components

10 kOhm [CRS0805-FX- 1002ELF]	10 kOhm [CRT0603-BY- 1002ELF]	10 kOhm [CRT0805-BY- 1002ELF]	10 kOhm [PWR163S-25- 1002F]
10 kOhm [CRS1206-FX- 1002ELF]	10 kOhm [CRT0603-DY- 1002ELF]	10 kOhm [CRT0805-DY- 1002ELF]	10 kOhm [PWR163S-25- 1002J]
10 kOhm [CRS1206-JX- 103ELF]	10 kOhm [CRT0603-DZ- 1002ELF]	10 kOhm [CRT0805-DZ- 1002ELF]	10 kOhm [PWR220T-20- 1002F]
10 kOhm [CRS2512-FX- 1002ELF]	10 kOhm [CRT0603-FX- 1002ELF]	10 kOhm [CRT0805-FV- 1002ELF]	10 kOhm [PWR220T-20- 1002J]
10 kOhm [CRT0402-BW- 1002GLF]	10 kOhm [CRT0603-FY- 1002ELF]	10 kOhm [CRT0805-FX- 1002ELF]	10 kOhm [PWR220T-35- 1002F]
10 kOhm [CRT0402-BY- 1002GLF]	10 kOhm [CRT0603-FZ- 1002ELF]	10 kOhm [CRT0805-FZ- 1002ELF]	10 kOhm [PWR220T-35- 1002J]
10 kOhm [CRT0402-BZ- 1002GAS]	10 kOhm [CRT0603-PV- 1002ELF]	10 kOhm [CRT1206-AV- 1002ELF]	10 kOhm [PWR221T-30- 1002F]
10 kOhm [CRT0402-FZ- 1002GLF]	10 kOhm [CRT0805-BV- 1002ELF]	10 kOhm [CRT1206-BW- 1002ELF]	10 kOhm [PWR221T-30- 1002J]
10 kOhm [CRT0603-BV- 1002ELF]	10 kOhm [CRT0805-BW- 1002ELF]	10 kOhm [CRT1206-BY- 1002ELF]	10 kOhm [PWR263S-20- 1002F]
10 kOhm [CRT0603-BW- 1002ELF]	10 kOhm [CRT0805-BX- 1002ELF]	10 kOhm [CRT1206-FZ- 1002ELF]	10 kOhm [PWR263S-20- 1002FE]
10 kOhm [CRT0603-BY- 1002EAS]	10 kOhm [CRT0805-BY- 1002EAS]	10 kOhm [CRT1206-PV- 1002ELF]	10 kOhm [PWR263S-20- 1002J]

Multisim 14.1 Base Edition Components

10 kOhm [PWR263S-35-1002F]	10 MOhm [4308R-102-106LF]	10 MOhm [CHV1206-JW-106ELF]	10 MOhm [CR1206-JW-106ELF]
10 kOhm [PWR263S-35-1002J]	10 MOhm [4309R-101-106LF]	10 MOhm [CHV2010-FX-1005ELF]	10 MOhm [CR1206-JW-106GLF]
10 kOhm [PWR4525W1002J]	10 MOhm [4606X-101-106LF]	10 MOhm [CHV2512-FX-1005ELF]	10 MOhm [CR2010-JW-106ELF]
10 kOhm [PWR4525W1002JE]	10 MOhm [4608X-102-106LF]	10 MOhm [CHV2512-JW-106ELF]	10 MOhm [CR2512-JW-106ELF]
10 mH [SDR0503-103JL]	10 MOhm [4609X-101-106LF]	10 MOhm [CR0201-JW-106GLF]	10 mOhm [CRA2512-FZ-R010ELF]
10 mH [SDR0906-103KL]	10 MOhm [4610X-101-106LF]	10 MOhm [CR0402-JW-106GLF]	10 mOhm [CRA2512-JZ-R010ELF]
10 mH [SDR1005-103KL]	10 MOhm [4610X-102-106LF]	10 MOhm [CR0603-FW-1005ELF]	10 mOhm [CRF0805-FX-R010ELF]
10 mH [SRE6603-103M]	10 MOhm [4816P-T01-106]	10 MOhm [CR0603-JW-106ELF]	10 mOhm [CRF1206-FX-R010ELF]
10 mH [SRR0906-103YL]	10 MOhm [4816P-T01-106LF]	10 MOhm [CR0805-FW-1005ELF]	10 mOhm [CRF2512-FX-R010ELF]
10 mH [SRR0908-103YL]	10 MOhm [CHV0603-JW-106ELF]	10 MOhm [CR0805-JW-106ELF]	10 mOhm [CRL2512-FU-R010ELF]
10 mH [SRR1208-103KL]	10 MOhm [CHV0805-FX-1005ELF]	10 MOhm [CR0805-JW-106ELF]	
10 mH [SRR6603-103ML]	10 MOhm [CHV0805-FX-1005ELF]	10 MOhm [CHV1206-FX-1005ELF]	
10 MOhm [4306R-101-106]	10 MOhm [CHV1206-FX-1005ELF]		
10 MOhm [4308R-102-106]			

Multisim 14.1 Base Edition Components

10 mOhm [CRL2512-JU- R010ELF]	10 mOhm [PWR4412- 2SCR0100J]	10 nF [05085C103KAT2V]	10 nF [C0402C103K4RACT U]
10 mOhm [PWR1913WR010F]	10 mOhm [PWR4412- 2SDR0100F]	10 nF [05086C103KAT2S]	10 nF [C0402C103K5RACT U]
10 mOhm [PWR1913WR010F E]	10 mOhm [PWR4412- 2SDR0100J]	10 nF [0508YC103KAT2S]	10 nF [C0402C103K8RACT U]
10 mOhm [PWR1913WR010J]	10 mOhm [PWR4525WR010J]	10 nF [06123C103KAT2S]	10 nF [C0402C103K9RACT U]
10 mOhm [PWR1913WR010JE]	10 mOhm [PWR4525WR010JE]	10 nF [06125C103KAT2V]	10 nF [C0603C103K1RACT U]
10 mOhm [PWR2615WR010F]	10 mOhm [PWR6327NR010FE]	10 nF [06126C103KAT2S]	10 nF [C0603C103K2RACT U]
10 mOhm [PWR2615WR010F E]	10 mOhm [PWR6327WR010J]	10 nF [0612ZC103KAT2S]	10 nF [C0603C103K3GACT U]
10 mOhm [PWR2615WR010J]	10 mOhm [PWR6327WR010JE]	10 nF [C0201C103K4PACT U]	10 nF [C0603C103K3HACT U]
10 mOhm [PWR2615WR010JE]	10 nF [03063C103KAT2A]	10 nF [C0201C103K8PACT U]	10 nF [C0603C103K3RACT U]
10 mOhm [PWR4412- 2SBR0100F]	10 nF [03066C103KAT2A]	10 nF [C0201C103K9PACT U]	10 nF [C0603C103K4RACT U]
10 mOhm [PWR4412- 2SBR0100J]	10 nF [0306YC103KAT2A]	10 nF [C0402C103K3RACT U]	10 nF [C0603C103K5RACT U]
10 mOhm [PWR4412- 2SCR0100F]	10 nF [0306ZC103KAT2A]		

Multisim 14.1 Base Edition Components

10 nF [C0603C103K8RACT U]	10 nF [C0805C103K5RACT U]	10 nF [C1206C103K1RACT U]	10 nF [C1206C103M5UAC TU]
10 nF [C0603C103K9RACT U]	10 nF [C0805C103K8RACT U]	10 nF [C1206C103K2RACT U]	10 nF [C1210C103K1RACT U]
10 nF [C0805C103K1GACT U]	10 nF [C0805C103KARACT U]	10 nF [C1206C103K3GACT U]	10 nF [C1210C103K2RACT U]
10 nF [C0805C103K1HACT U]	10 nF [C0805C103M1UAC TU]	10 nF [C1206C103K3HACT U]	10 nF [C1210C103K5GACT U]
10 nF [C0805C103K1RACT U]	10 nF [C0805C103M5UAC TU]	10 nF [C1206C103K3RACT U]	10 nF [C1210C103K5RACT U]
10 nF [C0805C103K3GACT U]	10 nF [C0805F103K1RACT U]	10 nF [C1206C103K4GACT U]	10 nF [C1210C103KARACT U]
10 nF [C0805C103K3HACT U]	10 nF [C0805F103K2RACT U]	10 nF [C1206C103K4RACT U]	10 nF [C1812C103K1GACT U]
10 nF [C0805C103K3RACT U]	10 nF [C0805F103K3RACT U]	10 nF [C1206C103K5HACT U]	10 nF [C1812C103K1RACT U]
10 nF [C0805C103K4RACT U]	10 nF [C0805F103K4RACT U]	10 nF [C1206C103K5RACT U]	10 nF [C1812C103K2RACT U]
10 nF [C0805C103K5GACT U]	10 nF [C0805F103K5RACT U]	10 nF [C1206C103KARACT U]	10 nF [C1812C103K5GACT U]
10 nF [C0805C103K5HACT U]	10 nF [C1206C103K1HACT U]	10 nF [C1206C103M1UAC TU]	10 nF [C1812C103K5RACT U]

Multisim 14.1 Base Edition Components

10 nF [C1825C103K1GACT U]	10 nF [GMC5.7102K250J3 1TR12]	10 nF [LD175C103KAB2V]	10 nF [PG124W103MAB2 S1]
10 nF [C1825C103K2GACT U]	10 nF [GMC5.7103K100J3 1TR12]	10 nF [LD17YC103KAB2S]	10 nF [PG124Z103MAB2S 1]
10 nF [C1825C103K5GACT U]	10 nF [GMC5.7103K50J31 TR12]	10 nF [LDEPD2100KA5N0 0]	10 nF [PG126D103MAB2S 1]
10 nF [C2220C103K1GACT U]	10 nF [GMC7.3102K250K3 1TR12]	10 nF [LG126Z103MAT2S 1]	10 nF [PG126W103MAB2 S1]
10 nF [C2220C103K2GACT U]	10 nF [GMC7.3103K100K3 1TR12]	10 nF [LG226C103MAT2S 1]	10 nF [PG126Z103MAB2S 1]
10 nF [C2225C103K2GACT U]	10 nF [GMC7.3103K400K3 5TR12]	10 nF [MMC5.7103K250J 31TR12]	10 nF [PG224C103MAB2S 1]
10 nF [C2225C103KCGAC TU]	10 nF [GMC7.3104K100K3 7TR12]	10 nF [MMC5.7103K50J3 1TR12]	10 nF [PG224D103MAB2S 1]
10 nF [CA064C103K3RACT U]	10 nF [GPC7.3103K63K31 TR12]	10 nF [MMC7.3103K250K 31TR12]	10 nF [PG224W103MAB2 S1]
10 nF [CA064C103K4RACT U]	10 nF [LD163C103KAB2A]	10 nF [MMC7.3103K400K 35TR12]	10 nF [PG224Z103MAB2S 1]
10 nF [CA064C103K5RACT U]	10 nF [LD166C103KAB2A]	10 nF [MMC7.3103K50K3 1TR12]	10 nF [PG226C103MAB2S 1]
10 nF [CA064C103K8RACT U]	10 nF [LD16ZC103KAB2A]	10 nF [MMC7.3103K63K3 1TR12]	10 nF [PG226D103MAB2S 1]
	10 nF [LD173C103KAB2S]	10 nF [PG124D103MAB2S 1]	

Multisim 14.1 Base Edition Components

10 nF [PG226W103MAB2 S1]	10 Ohm [4114R-1- 100]	10 Ohm [4308R- 102-100LF]	10 Ohm [4605X- 101-100LF]
10 nF [PG226Z103MAB2S 1]	10 Ohm [4114R-1- 100LF]	10 Ohm [4309R- 101-100LF]	10 Ohm [4606X- 101-100LF]
10 nF [PG22ZC103MAB2S 1]	10 Ohm [4114R-2- 100]	10 Ohm [4310M- 102-100LF]	10 Ohm [4606X- 102-100LF]
10 nF [SPC10.2103K100A 31TR16]	10 Ohm [4114R-2- 100LF]	10 Ohm [4310R- 101-100]	10 Ohm [4606X- AP2-100LF]
10 nF [SPC10.2103K250A 31TR16]	10 Ohm [4116R-1- 100]	10 Ohm [4310R- 101-100LF]	10 Ohm [4608H- 102-100LF]
10 nF [SPC10.2103K250A 31TR16]	10 Ohm [4116R-1- 100LF]	10 Ohm [4310R- 102-100]	10 Ohm [4608X- 101-100LF]
10 nF [SPC10.2103K400A 31TR16]	10 Ohm [4116R-2- 100]	10 Ohm [4310R- 102-100LF]	10 Ohm [4608X- 102-100LF]
10 nF [SPC10.2103K400A 31TR16]	10 Ohm [4306R- 101-100]	10 Ohm [4416P-1- 100]	10 Ohm [4608X- AP2-100LF]
10 nF [SPC10.2103K630A 31TR16]	10 Ohm [4306R- 101-100LF]	10 Ohm [4416P-1- 100LF]	10 Ohm [4609X- 101-100LF]
10 nF [SPC10.2103K630A 31TR16]	10 Ohm [4306R- 102-100]	10 Ohm [4416P-2- 100]	10 Ohm [4610X- 101-100LF]
10 nF [SPC7.3103K100K31 TR12]	10 Ohm [4306R- 102-100LF]	10 Ohm [4416P- T01-100]	10 Ohm [4610X- 102-100LF]
10 nF [SPC7.3103K250K35 TR12]	10 Ohm [4308H- 102-100]	10 Ohm [4420P-1- 100]	10 Ohm [4610X- AP2-100LF]
10 nF [W2F15C1038AT1A]	10 Ohm [4308R- 101-100]	10 Ohm [4420P-1- 100LF]	10 Ohm [4611X- 101-100LF]
10 nF [W2F15C1038AT1A]	10 Ohm [4308R- 101-100LF]	10 Ohm [4420P- T01-100]	10 Ohm [4612X- 102-100LF]
10 nF [W3F15C1038AT1A]	10 Ohm [4308R- 102-100]	10 Ohm [4604X- 102-100LF]	10 Ohm [4814P-1- 100]

Multisim 14.1 Base Edition Components

10 Ohm [4814P-1-100LF]	10 Ohm [CAT10-100J4LF]	10 Ohm [CAY17-100JALF]	10 Ohm [CR2010-FX-10R0ELF]
10 Ohm [4814P-T01-100]	10 Ohm [CAT16-100J2GLF]	10 Ohm [CR0201-JW-100GLF]	10 Ohm [CR2010-JW-100ELF]
10 Ohm [4814P-T01-100LF]	10 Ohm [CAT16-100J2LF]	10 Ohm [CR0402-FX-10R0GLF]	10 Ohm [CR2512-FX-10R0ELF]
10 Ohm [4816P-1-100]	10 Ohm [CAT16-100J4GLF]	10 Ohm [CR0402-JW-100GLF]	10 Ohm [CR2512-JW-100ELF]
10 Ohm [4816P-1-100F]	10 Ohm [CAT16-100J4LF]	10 Ohm [CR0603-FX-10R0ELF]	10 Ohm [CRM0805-JW-100ELF]
10 Ohm [4816P-1-100LF]	10 Ohm [CAT16-100J8LF]	10 Ohm [CR0603-FX-10R0GLF]	10 Ohm [CRM1206-FX-10R0ELF]
10 Ohm [4816P-2-100]	10 Ohm [CAT16-10R0F4LF]	10 Ohm [CR0603-JW-100ELF]	10 Ohm [CRM1206-JW-100ELF]
10 Ohm [4816P-2-100LF]	10 Ohm [CAT25-100JALF]	10 Ohm [CR0603-JW-100GLF]	10 Ohm [CRM2010-FX-10R0ELF]
10 Ohm [4816P-T01-100]	10 Ohm [CAY10-100J2LF]	10 Ohm [CR0805-FX-10R0ELF]	10 Ohm [CRM2512-FX-10R0ELF]
10 Ohm [4816P-T01-100LF]	10 Ohm [CAY10-100J4LF]	10 Ohm [CR0805-FX-10R0GLF]	10 Ohm [CRM2512-JW-100ELF]
10 Ohm [4816P-T02-100]	10 Ohm [CAY16-100J2LF]	10 Ohm [CR0805-JW-100ELF]	10 Ohm [CRS0805-FX-10R0ELF]
10 Ohm [4816P-T02-100LF]	10 Ohm [CAY16-100J4GLF]	10 Ohm [CR0805-JW-100GLF]	10 Ohm [CRS0805-JX-100ELF]
10 Ohm [4820P-1-100]	10 Ohm [CAY16-100J4LF]	10 Ohm [CR1206-FX-10R0ELF]	10 Ohm [CRS1206-JX-100ELF]
10 Ohm [4820P-1-100LF]	10 Ohm [CAY16-100J8LF]	10 Ohm [CR1206-JW-100ELF]	
10 Ohm [4820P-T01-100]	10 Ohm [CAY16-10R0F4LF]	10 Ohm [CR1206-JW-100GLF]	

Multisim 14.1 Base Edition Components

10 Ohm [CRS2010-FX-10R0ELF]	10 Ohm [FW10A10R0JA]	10 Ohm [PWR220T-20-10R0J]	10 Ohm [PWR263S-35-10R0F]
10 Ohm [CRS2010-JX-100ELF]	10 Ohm [FW20A10R0JA]	10 Ohm [PWR220T-35-10R0F]	10 Ohm [PWR263S-35-10R0FE]
10 Ohm [CRS2512-FX-10R0ELF]	10 Ohm [FW30A10R0JA]	10 Ohm [PWR220T-35-10R0J]	10 Ohm [PWR263S-35-10R0J]
10 Ohm [CRS2512-JX-100ELF]	10 Ohm [FW50A10R0JA]	10 Ohm [PWR221T-30-10R0F]	10 Ohm [PWR3014W10R0JE]
10 Ohm [CRT0402-BY-10R0GLF]	10 Ohm [FW70A10R0JA]	10 Ohm [PWR221T-30-10R0J]	10 Ohm [PWR4318W10R0JE]
10 Ohm [CRT0402-FZ-10R0GLF]	10 Ohm [PWR163S-25-10R0F]	10 Ohm [PWR221T-50-10R0F]	10 Ohm [PWR4525W10R0F]
10 Ohm [CRT0603-BY-10R0ELF]	10 Ohm [PWR163S-25-10R0FE]	10 Ohm [PWR2615W10R0F]	10 Ohm [PWR4525W10R0J]
10 Ohm [CRT0603-FY-10R0ELF]	10 Ohm [PWR163S-25-10R0J]	10 Ohm [PWR2615W10R0J]	10 Ohm [PWR4525W10R0JE]
10 Ohm [CRT0603-FZ-10R0ELF]	10 Ohm [PWR163S-25-10R0JE]	10 Ohm [PWR2615W10R0JE]	10 Ohm [PWR5322W10R0JE]
10 Ohm [CRT0805-BW-10R0ELF]	10 Ohm [PWR1913W10R0J]	10 Ohm [PWR263S-20-10R0F]	10 Ohm [PWR6327W10R0J]
10 Ohm [CRT0805-BY-10R0ELF]	10 Ohm [PWR1913W10R0JE]	10 Ohm [PWR263S-20-10R0FE]	10 Ohm [PWR6327W10R0JE]
10 Ohm [CRT0805-CX-10R0ELF]	10 Ohm [PWR2010W10R0JE]	10 Ohm [PWR263S-20-10R0J]	10 pF [C0402C100K3GACTU]
10 Ohm [CRT0805-CY-10R0ELF]	10 Ohm [PWR220T-20-10R0F]		
10 Ohm [CRT1206-BY-10R0ELF]			
10 Ohm [CRT1206-DW-10R0ELF]			

Multisim 14.1 Base Edition Components

10 pF [C0402C100K4GACT U]	10 pF [C0805C100KDGAC TU]	10 pF [C2220C100KBGAC TU]	10 uF [C0805C106K8PACT U]
10 pF [C0402C100K5GACT U]	10 pF [C0805H100K5GAC TU]	10 pF [C2225C100KBGAC TU]	10 uF [C0805C106K9PACT U]
10 pF [C0402C100K8GACT U]	10 pF [C1206C100K1GACT U]	10 pF [CA064C100K1GAC TU]	10 uF [C0805C106M9VAC TU]
10 pF [C0603C100K1GACT U]	10 pF [C1206C100K2GACT U]	10 pF [CA064C100K2GAC TU]	10 uF [C1206C106K3PACT U]
10 pF [C0603C100K2GACT U]	10 pF [C1206C100K5GACT U]	10 pF [CA064C100K4GAC TU]	10 uF [C1206C106K4PACT U]
10 pF [C0603C100K3GACT U]	10 pF [C1206C100KBGAC TU]	10 pF [CA064C100K5GAC TU]	10 uF [C1206C106K4RACT U]
10 pF [C0603C100K5GACT U]	10 pF [C1210C100K2GACT U]	10 uF [12TPC10M] 10 uF [16TQC10M]	10 uF [C1206C106K8PACT U]
10 pF [C0805C100K1GACT U]	10 pF [C1210C100K5GACT U]	10 uF [35TQC10M] 10 uF [6TPU10MSI]	10 uF [C1206C106K8RACT U]
10 pF [C0805C100K2GACT U]	10 pF [C1210C100KBGAC TU]	10 uF [A700V106M016AT E045]	10 uF [C1206C106K9PACT U]
10 pF [C0805C100K5GACT U]	10 pF [C1812C100KBGAC TU]	10 uF [A700V106M12RAT E060]	10 uF [C1206C106K9RACT U]
10 pF [C0805C100KBGAC TU]	10 pF [C1825C100KBGAC TU]	10 uF [C0805C106K4PACT U]	10 uF [C1206C106M8VAC TU]

Multisim 14.1 Base Edition Components

10 uF [C1206C106M9VAC TU]	10 uF [C1210C106M8VAC TU]	10 uF [NOJA106K006RWJ]	10 uF [T491C106M010AT]
10 uF [C1210C106K3PACT U]	10 uF [C1210C106M9VAC TU]	10 uF [NOSA106K006R20 00]	10 uF [T491C106M016AT]
10 uF [C1210C106K3RACT U]	10 uF [EEFCS1D100R]	10 uF [T429E106M020AH 4250]	10 uF [T491C106M020AT]
10 uF [C1210C106K4PACT U]	10 uF [EEFCS1E100R]	10 uF [T429H106M035AH 4250]	10 uF [T491C106M025AT]
10 uF [C1210C106K4RACT U]	10 uF [EEFCS1V100R]	10 uF [T491A106M004AT]	10 uF [T491D106M025AT]
10 uF [C1210C106K8NAC TU]	10 uF [EEHZA1H100R]	10 uF [T491A106M006AT]	10 uF [T491D106M035AT]
10 uF [C1210C106K8PACT U]	10 uF [EEHZA1J100P]	10 uF [T491A106M010AT]	10 uF [T491D106M050AT]
10 uF [C1210C106K8RACT U]	10 uF [EEHZC1H100R]	10 uF [T491A106M016AT]	10 uF [T491S106M004AT]
10 uF [C1210C106K8PACT U]	10 uF [EEHZC1J100P]	10 uF [T491A106M020AT]	10 uF [T491S106M006AT]
10 uF [C1210C106K8RACT U]	10 uF [MDC10106K100A5 8P7TUBE]	10 uF [T491B106M004AT]	10 uF [T491S106M010AT]
10 uF [C1210C106K9PACT U]	10 uF [MDC10106K100A5 8P8TUBE]	10 uF [T491B106M006AT]	10 uF [T491T106M006AT]
10 uF [C1210C106K9RACT U]	10 uF [MDC10106K50A57 P7TUBE]	10 uF [T491B106M010AT]	10 uF [T491T106M010AT]
10 uF [C1210C106M4VAC TU]	10 uF [MDC10106K50A57 P8TUBE]	10 uF [T491B106M016AT]	10 uF [T491T106M016AT]

Multisim 14.1 Base Edition Components

10 uF [T491U106M016AT]	10 uF [T494B106M020AT]	10 uF [T494T106M016AT]	10 uF [T495D106M035AT E125]
10 uF [T491U106M020AT]	10 uF [T494C106M010AT]	10 uF [T494U106M016AT]	10 uF [T495D106M035AT E250]
10 uF [T491V106M035AT]	10 uF [T494C106M016AT]	10 uF [T494U106M020AT]	10 uF [T495D106M035AT E300]
10 uF [T491X106M050AT]	10 uF [T494C106M020AT]	10 uF [T494V106M035AT]	10 uF [T495T106M016AT E4K0]
10 uF [T493C106M020AH 6110]	10 uF [T494C106M025AT]	10 uF [T494X106M050AT]	10 uF [T495X106M035AT E200]
10 uF [T494A106M004AT]	10 uF [T494D106M025AT]	10 uF [T495A106M010AT E1K8]	10 uF [T495X106M035AT E250]
10 uF [T494A106M006AT]	10 uF [T494D106M035AT]	10 uF [T495B106M010AT E750]	10 uF [T495X106M050AT E250]
10 uF [T494A106M010AT]	10 uF [T494D106M050AT]	10 uF [T495B106M020AT E1K0]	10 uF [T495X106M050AT E260]
10 uF [T494A106M016AT]	10 uF [T494S106M004AT]	10 uF [T495C106M020AT E400]	10 uF [T495X106M050AT E300]
10 uF [T494B106M004AT]	10 uF [T494S106M006AT]	10 uF [T495C106M020AT E475]	10 uF [T496D106M025AT 6110]
10 uF [T494B106M006AT]	10 uF [T494S106M010AT]	10 uF [T495C106M025AT E275]	10 uF [T497F106M015AT 6110]
10 uF [T494B106M010AT]	10 uF [T494T106M006AT]	10 uF [T495C106M025AT E450]	
10 uF [T494B106M016AT]	10 uF [T494T106M010AT]		

Multisim 14.1 Base Edition Components

10 uF [T498B106M006AT E2K1]	10 uF [T520B106M016AT E100]	10 uF [TAJA106K016RNJ]	10 uF [TAJE106K050RNJ]
10 uF [T498B106M010AT E1K8]	10 uF [T521D106M050AT E090]	10 uF [TAJB106K006RNJ]	10 uF [TAJP106K010RNJ]
10 uF [T498B106M016AT E2K8]	10 uF [T521X106M063AT E050]	10 uF [TAJB106K016RNJ]	10 uF [TAJR106K004RNJ]
10 uF [T498C106M016AT E1K4]	10 uF [T541X106M063AH 6510]	10 uF [TAJB106K020RNJ]	10 uF [TAJS106K002RNJ]
10 uF [T498C106M020AT E1K1]	10 uF [TACL106K002RTA]	10 uF [TAJB106K025RNJ]	10 uF [TAJS106K004RNJ]
10 uF [T498C106M025AT E1K1]	10 uF [TACL106K003RTA]	10 uF [TAJC106K010RNJ]	10 uF [TAJS106K006RNJ]
10 uF [T498D106M035AT E700]	10 uF [TACL106K006RTA]	10 uF [TAJC106K016RNJ]	10 uF [TAJS106K010RNJ]
10 uF [T498D106M050AT E1K0]	10 uF [TACR106K004RTA]	10 uF [TAJC106K020RNJ]	10 uF [TAJT106K004RNJ]
10 uF [T498D106M050AT E1K0]	10 uF [TACR106K006RTA]	10 uF [TAJC106K025RNJ]	10 uF [TAJT106K006RNJ]
10 uF [T510X106M050AT E090]	10 uF [TACR106K010RTA]	10 uF [TAJC106K035RNJ]	10 uF [TAJT106K010RNJ]
10 uF [T510X106M050AT E120]	10 uF [TACR106K016RTA]	10 uF [TAJD106K025RNJ]	10 uF [TAJT106K016RNJ]
10 uF [T520A106M010AT E080]	10 uF [TAJA106K004RNJ]	10 uF [TAJD106K035RNJ]	10 uF [TAJW106K016RNJ]
	10 uF [TAJA106K006RNJ]	10 uF [TAJD106K050RNJ]	10 uF [TAJW106K020RNJ]
	10 uF [TAJA106K010RNJ]	10 uF [TAJE106K035RNJ]	10 uF [TAJW106K025RNJ]

Multisim 14.1 Base Edition Components

10 uF [TAJX106K035RNJ]	10 uF [TPSB106K016R050 0]	10 uF [TPSD106K035R012 5]	10 uF [TPST106K010R100 0]
10 uF [TAJY106K035RNJ]	10 uF [TPSB106K016R080 0]	10 uF [TPSD106K035R030 0]	10 uF [TPST106K010R200 0]
10 uF [THJB106K016RJN]			
10 uF [THJC106K025RJN]	10 uF [TPSB106K020R100 0]	10 uF [TPSD106K050R050 0]	10 uF [TPST106K016R080 0]
10 uF [THJD106K035RJN]	10 uF [TPSB106K025R180 0]	10 uF [TPSE106K035R020 0]	10 uF [TPST106K016R100 0]
10 uF [THJE106K050RJN]	10 uF [TPSC106K016R050 0]	10 uF [TPSE106K050R040 0]	10 uF [TPSW106K016R06 00]
10 uF [TPMD106K050R01 40]	10 uF [TPSC106K020R050 0]	10 uF [TPSE106K050R050 0]	10 uF [TRJA106K010RRJ]
10 uF [TPME106K050R01 20]	10 uF [TPSC106K020R070 0]	10 uF [TPSR106K004R300 0]	10 uF [TRJB106K010RRJ]
10 uF [TPSA106K006R150 0]	10 uF [TPSC106K025R030 0]	10 uF [TPSR106K006R100 0]	10 uF [TRJB106K016RRJ]
10 uF [TPSA106K010R090 0]	10 uF [TPSC106K025R050 0]	10 uF [TPSR106K006R150 0]	10 uF [TRJB106K020RRJ]
10 uF [TPSA106K010R180 0]	10 uF [TPSC106K035R060 0]	10 uF [TPSR106K006R300 0]	10 uF [TRJC106K020RRJ]
10 uF [TPSA106K016R100 0]	10 uF [TPSD106K025R050 0]	10 uF [TPST106K006R100 0]	10 uF [TRJC106K025RRJ]
10 uF [TPSB106K010R100 0]			10 uF [TRJD106K035RRJ]

Multisim 14.1 Base Edition Components

10 uF [TRJE106K050RRJ]	10 uH [SDR1030- 100M]	10 uH [SRN4026- 100M]	10 uH [SRP5015TA- 100M]
10 uH [SDE0403A- 100M]	10 uH [SDR1045- 100M]	10 uH [SRN5020- 100M]	10 uH [SRP5030T- 100M]
10 uH [SDE0604A- 100M]	10 uH [SDR1105- 100ML]	10 uH [SRN5040- 100M]	10 uH [SRP5030TA- 100M]
10 uH [SDE0805A- 100M]	10 uH [SDR1305- 100M]	10 uH [SRN6028- 100M]	10 uH [SRP6540- 100M]
10 uH [SDE1006A- 100M]	10 uH [SDR1307- 100ML]	10 uH [SRN6045- 100M]	10 uH [SRP7028A- 100M]
10 uH [SDR0302- 100ML]	10 uH [SDR1307A- 100M]	10 uH [SRN8040- 100M]	10 uH [SRP7030- 100FM]
10 uH [SDR0403- 100ML]	10 uH [SDR1806- 100ML]	10 uH [SRP1038A- 100M]	10 uH [SRP7050TA- 100M]
10 uH [SDR0503- 100ML]	10 uH [SDR6603- 100M]	10 uH [SRP1040- 100M]	10 uH [SRR0603- 100ML]
10 uH [SDR0603- 100ML]	10 uH [SDR7030- 100M]	10 uH [SRP1235- 100M]	10 uH [SRR0604- 100ML]
10 uH [SDR0604- 100ML]	10 uH [SDR7045- 100M]	10 uH [SRP1245A- 100M]	10 uH [SRR0618- 100ML]
10 uH [SDR0703- 100KL]	10 uH [SRN1060- 100M]	10 uH [SRP1250- 100M]	10 uH [SRR0735A- 100M]
10 uH [SDR0805- 100ML]	10 uH [SRN3010- 100M]	10 uH [SRP1270- 100M]	10 uH [SRR0745A- 100M]
10 uH [SDR0906- 100ML]	10 uH [SRN3015- 100M]	10 uH [SRP1770TA- 100M]	10 uH [SRR0804- 100M]
10 uH [SDR1005- 100ML]	10 uH [SRN4012T- 100M]	10 uH [SRP4012TA- 100M]	10 uH [SRR0805- 100M]
10 uH [SDR1006- 100ML]	10 uH [SRN4018- 100M]	10 uH [SRP4020TA- 100M]	10 uH [SRR0905- 100M]

Multisim 14.1 Base Edition Components

10 uH [SRR0906-100ML]	10 uH [SRR4011-100YL]	10 uH [SRU1048-100Y]	10 uH [SRU5028-100Y]
10 uH [SRR0908-100ML]	10 uH [SRR4018-100Y]	10 uH [SRU1048A-100Y]	10 uH [SRU5028A-100Y]
10 uH [SRR1003-100M]	10 uH [SRR4028-100Y]	10 uH [SRU1063-100Y]	10 uH [SRU6011-100Y]
10 uH [SRR1005-100M]	10 uH [SRR5018-100Y]	10 uH [SRU2009-100Y]	10 uH [SRU6018-100Y]
10 uH [SRR1205-100ML]	10 uH [SRR5028-100Y]	10 uH [SRU2011-100Y]	10 uH [SRU6025-100Y]
10 uH [SRR1206-100ML]	10 uH [SRR6028-100Y]	10 uH [SRU2013-100Y]	10 uH [SRU6025A-100Y]
10 uH [SRR1208-100ML]	10 uH [SRR6038-100Y]	10 uH [SRU2016-100Y]	10 uH [SRU8028-100Y]
10 uH [SRR1210-100M]	10 uH [SRR6040A-100M]	10 uH [SRU3011-100Y]	10 uH [SRU8028A-100Y]
10 uH [SRR1210A-100M]	10 uH [SRR6603-100ML]	10 uH [SRU3014-100Y]	10 uH [SRU8043-100Y]
10 uH [SRR1240-100M]	10 uH [SRR7032-100M]	10 uH [SRU3017-100Y]	10.1 kOhm [CRT1206-BY-1012ELF]
10 uH [SRR1260-100M]	10 uH [SRR7045-100M]	10 uH [SRU3028-100Y]	10.2 kOhm [CR0402-FX-1022GLF]
10 uH [SRR1260A-100M]	10 uH [SRU1028-100Y]	10 uH [SRU3028A-100Y]	10.2 kOhm [CR0603-FX-1022ELF]
10 uH [SRR1280-100M]	10 uH [SRU1028A-100Y]	10 uH [SRU5011-100Y]	10.2 kOhm [CR0805-FX-1022ELF]
10 uH [SRR1806-100M]	10 uH [SRU1038-100Y]	10 uH [SRU5016-100Y]	
10 uH [SRR3011-100YL]	10 uH [SRU1038A-100Y]	10 uH [SRU5018-100Y]	

Multisim 14.1 Base Edition Components

10.2 kOhm [CR1206-FX-1022ELF]	10.5 Ohm [CR0805-FX-10R5ELF]	100 kOhm [4108R-1-104LF]	100 kOhm [4306M-102-104]
10.2 kOhm [CRT0402-BW-1022GLF]	10.5 Ohm [CR0805-FX-10R5GLF]	100 kOhm [4114R-1-104]	100 kOhm [4306M-102-104LF]
10.2 kOhm [CRT0805-BY-1022ELF]	10.5 Ohm [CR1206-FX-10R5ELF]	100 kOhm [4114R-1-104LF]	100 kOhm [4306R-101-104]
10.2 kOhm [CRT0805-DZ-1022ELF]	10.5 Ohm [PWR6327N10R5FE]	100 kOhm [4114R-2-104]	100 kOhm [4306R-101-104LF]
10.2 Ohm [CR0805-FX-10R2ELF]	10.7 kOhm [CR0402-FX-1072GLF]	100 kOhm [4114R-2-104LF]	100 kOhm [4306R-102-104]
10.2 Ohm [CR1206-FX-10R2ELF]	10.7 kOhm [CR0603-FX-1072ELF]	100 kOhm [4116R-1-104]	100 kOhm [4306R-102-104LF]
10.5 kOhm [CR0402-FX-1052GLF]	10.7 kOhm [CR0805-FX-1072ELF]	100 kOhm [4116R-1-104LF]	100 kOhm [4308H-101-104]
10.5 kOhm [CR0603-FX-1052ELF]	10.7 kOhm [CR1206-FX-1072ELF]	100 kOhm [4116R-2-104]	100 kOhm [4308H-102-104]
10.5 kOhm [CR0805-FX-1052ELF]	10.7 kOhm [CR0805-FX-1072ELF]	100 kOhm [4116R-2-104LF]	100 kOhm [4308H-102-104LF]
10.5 kOhm [CR1206-FX-1052ELF]	10.7 kOhm [CR1206-FX-1072ELF]	100 kOhm [4304M-101-104]	100 kOhm [4308M-102-104]
10.5 kOhm [CR0805-FX-1052ELF]	10.7 kOhm [CRT0402-BY-1072GLF]	100 kOhm [4304M-101-104LF]	100 kOhm [4308M-102-104LF]
10.5 kOhm [CR1206-FX-1052ELF]	10.7 kOhm [CRT0805-DZ-1072ELF]	100 kOhm [4304M-102-104]	100 kOhm [4308R-101-104]
10.5 kOhm [CRT0402-FZ-1052GLF]	10.7 Ohm [CR1206-FX-10R7ELF]	100 kOhm [4304M-102-104LF]	100 kOhm [4308R-101-104LF]
10.5 kOhm [CRT0805-CX-1052ELF]	10 AMP	100 kOhm [4306H-101-104]	100 kOhm [4308R-102-104]
	100 kOhm [4108R-1-104]	100 kOhm [4306H-101-104LF]	100 kOhm [4308R-102-104LF]

Multisim 14.1 Base Edition Components

100 kOhm [4309R-101-104]	100 kOhm [4416P-1-104]	100 kOhm [4606H-101-104LF]	100 kOhm [4609M-101-104LF]
100 kOhm [4309R-101-104LF]	100 kOhm [4416P-2-104]	100 kOhm [4606H-102-104LF]	100 kOhm [4609X-101-104LF]
100 kOhm [4310H-101-104]	100 kOhm [4416P-T01-104]	100 kOhm [4606M-101-104LF]	100 kOhm [4609X-AP1-104LF]
100 kOhm [4310H-101-104LF]	100 kOhm [4416P-T02-104]	100 kOhm [4606M-102-104LF]	100 kOhm [4610H-101-104LF]
100 kOhm [4310H-102-104]	100 kOhm [4420P-1-104]	100 kOhm [4606X-101-104LF]	100 kOhm [4610M-101-104LF]
100 kOhm [4310H-102-104LF]	100 kOhm [4420P-1-104LF]	100 kOhm [4606X-102-104LF]	100 kOhm [4610M-102-104LF]
100 kOhm [4310M-101-104]	100 kOhm [4420P-2-104]	100 kOhm [4606X-AP1-104LF]	100 kOhm [4610X-101-104LF]
100 kOhm [4310M-101-104LF]	100 kOhm [4420P-2-104LF]	100 kOhm [4606X-AP2-104LF]	100 kOhm [4610X-102-104LF]
100 kOhm [4310M-102-104]	100 kOhm [4420P-T01-104]	100 kOhm [4607X-101-104LF]	100 kOhm [4610X-AP1-104LF]
100 kOhm [4310R-101-104]	100 kOhm [4420P-T02-104]	100 kOhm [4608H-102-104LF]	100 kOhm [4610X-AP2-104LF]
100 kOhm [4310R-101-104LF]	100 kOhm [4604X-101-104LF]	100 kOhm [4608M-102-104LF]	100 kOhm [4611X-101-104LF]
100 kOhm [4310R-102-104]	100 kOhm [4604X-102-104LF]	100 kOhm [4608X-101-104LF]	100 kOhm [4612X-101-104LF]
100 kOhm [4310R-102-104LF]	100 kOhm [4605H-101-104LF]	100 kOhm [4608X-102-104LF]	100 kOhm [4612X-102-104LF]
100 kOhm [4311R-101-104]	100 kOhm [4605X-101-104LF]	100 kOhm [4608X-AP1-104LF]	100 kOhm [4613X-101-104LF]
100 kOhm [4311R-101-104LF]	100 kOhm [4605X-AP1-104LF]	100 kOhm [4608X-AP2-104LF]	100 kOhm [4614X-102-104LF]

Multisim 14.1 Base Edition Components

100 kOhm [4814P-1-104]	100 kOhm [4816P-T01-104LF]	100 kOhm [CAT10-104J4LF]	100 kOhm [CHV0603-JW-104ELF]
100 kOhm [4814P-1-104LF]	100 kOhm [4816P-T02-104]	100 kOhm [CAT16-1003F4LF]	100 kOhm [CHV0805-FX-1003ELF]
100 kOhm [4814P-2-104]	100 kOhm [4816P-T02-104LF]	100 kOhm [CAT16-1003F8LF]	100 kOhm [CHV0805-JW-104ELF]
100 kOhm [4814P-2-104LF]	100 kOhm [4818P-1-104]	100 kOhm [CAT16-104J2LF]	100 kOhm [CHV1206-FX-1003ELF]
100 kOhm [4814P-T01-104]	100 kOhm [4818P-1-104LF]	100 kOhm [CAT16-104J4LF]	100 kOhm [CHV1206-JW-104ELF]
100 kOhm [4814P-T01-104LF]	100 kOhm [4818P-2-104]	100 kOhm [CAT16-104J8LF]	100 kOhm [CHV2010-FX-1003ELF]
100 kOhm [4814P-T02-104]	100 kOhm [4818P-2-104LF]	100 kOhm [CAT25-104JALF]	100 kOhm [CHV2010-JW-104ELF]
100 kOhm [4814P-T02-104LF]	100 kOhm [4818P-T01-104]	100 kOhm [CAY10-104J2LF]	100 kOhm [CHV2010-JW-104ELF]
100 kOhm [4816P-1-104]	100 kOhm [4818P-T02-104]	100 kOhm [CAY10-104J4LF]	100 kOhm [CHV2512-FX-1003ELF]
100 kOhm [4816P-1-104DLF]	100 kOhm [4820P-1-104]	100 kOhm [CAY16-1003F4LF]	100 kOhm [CR0201-FW-1003GLF]
100 kOhm [4816P-1-104F]	100 kOhm [4820P-1-104LF]	100 kOhm [CAY16-104J2LF]	100 kOhm [CR0201-JW-104GLF]
100 kOhm [4816P-1-104LF]	100 kOhm [4820P-2-104]	100 kOhm [CAY16-104J4GLF]	100 kOhm [CR0402-FX-1003GLF]
100 kOhm [4816P-2-104]	100 kOhm [4820P-2-104LF]	100 kOhm [CAY16-104J4LF]	
100 kOhm [4816P-2-104LF]	100 kOhm [4820P-T01-104]	100 kOhm [CAY16-104J8LF]	
100 kOhm [4816P-T01-104]	100 kOhm [4820P-T02-104]	100 kOhm [CAY17-104JALF]	

Multisim 14.1 Base Edition Components

100 kOhm [CR0402-JW- 104GLF]	100 kOhm [CR1206-FX- 1003GLF]	100 kOhm [CRT0402-DZ- 1003GAS]	100 kOhm [CRT1206-DY- 1003ELF]
100 kOhm [CR0603-FX- 1003ELF]	100 kOhm [CR1206-JW- 104ELF]	100 kOhm [CRT0402-FZ- 1003GLF]	100 kOhm [CRT1206-FZ- 1003ELF]
100 kOhm [CR0603-FX- 1003GLF]	100 kOhm [CR1206-JW- 104GLF]	100 kOhm [CRT0603-BY- 1003ELF]	100 kOhm [CRT1206-PY- 1003ELF]
100 kOhm [CR0603-FX- 1003HLF]	100 kOhm [CR2010-JW- 104ELF]	100 kOhm [CRT0603-FY- 1003ELF]	100 kOhm [PWR220T-20- 1003F]
100 kOhm [CR0603-JW- 104ELF]	100 kOhm [CR2512-JW- 104ELF]	100 kOhm [CRT0603-FZ- 1003ELF]	100 kOhm [PWR220T-20- 1003J]
100 kOhm [CR0603-JW- 104GLF]	100 kOhm [CRM1206-FX- 1003ELF]	100 kOhm [CRT0805-BY- 1003ELF]	100 kOhm [PWR263S-20- 1003F]
100 kOhm [CR0805-FX- 1003ELF]	100 kOhm [CRM2010-FX- 1003ELF]	100 kOhm [CRT0805-BZ- 1003ELF]	100 kOhm [PWR263S-20- 1003J]
100 kOhm [CR0805-FX- 1003GLF]	100 kOhm [CRM2512-FX- 1003ELF]	100 kOhm [CRT0805-DY- 1003ELF]	100 kOhm [PWR263S-35- 1003F]
100 kOhm [CR0805-JW- 104ELF]	100 kOhm [CRM2512-JW- 104ELF]	100 kOhm [CRT0805-DZ- 1003ELF]	100 kOhm [PWR263S-35- 1003J]
100 kOhm [CR0805-JW- 104GLF]	100 kOhm [CRT0402-BY- 1003GLF]	100 kOhm [CRT1206-BY- 1003EAS]	100 MOhm [CHV2512-JW- 107ELF]
100 kOhm [CR1206-FX- 1003ELF]	100 kOhm [CRT0402-CZ- 1003GLF]	100 kOhm [CRT1206-BY- 1003ELF]	100 mOhm [CRA2512-FZ- R100ELF]

Multisim 14.1 Base Edition Components

100 mOhm [CRA2512-JZ- R100ELF]	100 mOhm [CRM0805-FX- R100ELF]	100 mOhm [PWR1913WR100F E]	100 mOhm [PWR2615WR100J]
100 mOhm [CRL0603-FW- R100ELF]	100 mOhm [CRM0805-JX- R100ELF]	100 mOhm [PWR1913WR100J]	100 mOhm [PWR2615WR100JE]
100 mOhm [CRL0603-JW- R100ELF]	100 mOhm [CRM1206-FX- R100ELF]	100 mOhm [PWR1913WR100JE]	100 mOhm [PWR263S-35- R100F]
100 mOhm [CRL0805-FW- R100ELF]	100 mOhm [CRM2010-FX- R100ELF]	100 mOhm [PWR2010WR100F E]	100 mOhm [PWR263S-35- R100FE]
100 mOhm [CRL0805-JW- R100ELF]	100 mOhm [CRM2512-FX- R100ELF]	100 mOhm [PWR2010WR100JE]	100 mOhm [PWR3014WR100JE]
100 mOhm [CRL1206-FW- R100ELF]	100 mOhm [CRM2512-JX- R100ELF]	100 mOhm [PWR220T-20- R100F]	100 mOhm [PWR4318WR100JE]
100 mOhm [CRL1206-JW- R100ELF]	100 mOhm [PWR163S-25- R100F]	100 mOhm [PWR220T-20- R100J]	100 mOhm [PWR4412- 2SBR1000F]
100 mOhm [CRL2010-FW- R100ELF]	100 mOhm [PWR163S-25- R100FE]	100 mOhm [PWR220T-35- R100F]	100 mOhm [PWR4412- 2SBR1000J]
100 mOhm [CRL2010-JW- R100ELF]	100 mOhm [PWR163S-25- R100J]	100 mOhm [PWR221T-30- R100F]	100 mOhm [PWR4412- 2SCR1000F]
100 mOhm [CRL2512-FW- R100ELF]	100 mOhm [PWR163S-25- R100JE]	100 mOhm [PWR221T-30- R100J]	100 mOhm [PWR4412- 2SCR1000J]
100 mOhm [CRL2512-JW- R100ELF]	100 mOhm [PWR1913WR100F]	100 mOhm [PWR2615WR100F]	100 mOhm [PWR4412- 2SDR1000F]
		100 mOhm [PWR2615WR100F E]	

Multisim 14.1 Base Edition Components

100 mOhm [PWR4412- 2SDR1000J]	100 nF [05086C104KAT2S]	100 nF [C0402C104K9PACT U]	100 nF [C0805C104K3RACT U]
100 mOhm [PWR4525WR100F]	100 nF [0508YC104KAT2V]	100 nF [C0402C104K9RACT U]	100 nF [C0805C104K4RACT U]
100 mOhm [PWR4525WR100J]	100 nF [0508ZC104KAT2S]	100 nF [C0603C104K3RACT U]	100 nF [C0805C104K5RACT U]
100 mOhm [PWR4525WR100JE]	100 nF [06123C104KAT2V]	100 nF [C0603C104K4RACT U]	100 nF [C0805C104K8RACT U]
100 mOhm [PWR5322WR100JE]	100 nF [06125C104KAT2W]	100 nF [C0603C104K5RACT U]	100 nF [C0805C104K9RACT U]
100 mOhm [PWR6327WR100F E]	100 nF [06126C104KAT2S]	100 nF [C0603C104K8RACT U]	100 nF [C0805C104M3VAC TU]
100 mOhm [PWR6327WR100J]	100 nF [0612YC104KAT2S]	100 nF [C0603C104K9RACT U]	100 nF [C0805C104M4VAC TU]
100 mOhm [PWR6327WR100JE]	100 nF [0612ZC104KAT2S]	100 nF [C0603C104M3VAC TU]	100 nF [C0805C104M5UAC TU]
100 nF [03066C104KAT2A]	100 nF [C0201C104K9PACT U]	100 nF [C0603C104M4VAC TU]	100 nF [C0805C104M5VAC TU]
100 nF [0306YD104KAT2A]	100 nF [C0402C104K4PACT U]	100 nF [C0603C104M8VAC TU]	100 nF [C1206C104K1RACT U]
100 nF [0306ZC104KAT2A]	100 nF [C0402C104K4RACT U]	100 nF [C0603C104K1RACT U]	100 nF [C1206C104K2RACT U]
100 nF [05083C104KAT2A]	100 nF [C0402C104K8PACT U]		
100 nF [05085C104KAT2A]	100 nF [C0402C104K8RACT U]		

Multisim 14.1 Base Edition Components

100 nF [C1206C104K3GACT U]	100 nF [C1206F104K4RACT U]	100 nF [C1210C104K5HACT U]	100 nF [C1812C104K1GACT U]
100 nF [C1206C104K3HACT U]	100 nF [C1206F104K5RACT U]	100 nF [C1210C104K5RACT U]	100 nF [C1812C104K1HACT U]
100 nF [C1206C104K3RACT U]	100 nF [C1210C104K1GACT U]	100 nF [C1210C104K8RACT U]	100 nF [C1812C104K1R1C7 186]
100 nF [C1206C104K4RACT U]	100 nF [C1210C104K1HACT U]	100 nF [C1210C104KARACT U]	100 nF [C1812C104K1RACT U]
100 nF [C1206C104K5RACT U]	100 nF [C1210C104K1RACT U]	100 nF [C1210C104M1UAC TU]	100 nF [C1812C104K2RACT U]
100 nF [C1206C104KARACT U]	100 nF [C1210C104K2RACT U]	100 nF [C1210C104M5UAC TU]	100 nF [C1812C104K5GACT U]
100 nF [C1206C104M1UAC TU]	100 nF [C1210C104K3GACT U]	100 nF [C1210F104K1RACT U]	100 nF [C1812C104K5HACT U]
100 nF [C1206C104M5UAC TU]	100 nF [C1210C104K3HACT U]	100 nF [C1210F104K2RACT U]	100 nF [C1812C104K5RACT U]
100 nF [C1206F104K1RACT U]	100 nF [C1210C104K3RACT U]	100 nF [C1210F104K3RACT U]	100 nF [C1812C104M1UAC TU]
100 nF [C1206F104K2RACT U]	100 nF [C1210C104K4RACT U]	100 nF [C1210F104K4RACT U]	100 nF [C1812F104K1RACT U]
100 nF [C1206F104K3RACT U]	100 nF [C1210C104K5GACT U]	100 nF [C1210F104K5RACT U]	100 nF [C1812F104K2RACT U]

Multisim 14.1 Base Edition Components

100 nF [C1812F104K3RACT U]	100 nF [CA064C104K8RACT U]	100 nF [MDC10104K100A5 2P3TUBE]	100 nF [MDK10104K100A5 2P3TUBE]
100 nF [C1812F104K5RACT U]	100 nF [GMC5.7104K50J31 TR12]	100 nF [MDC10104K250A5 2P3TUBE]	100 nF [MDK10104K250A5 2P3TUBE]
100 nF [C1825C104K1RACT U]	100 nF [GMC7.3102K400K3 1TR12]	100 nF [MDC10104K400A5 2P3TUBE]	100 nF [MDK10104K400A5 2P3TUBE]
100 nF [C1825C104K2RACT U]	100 nF [GMC7.3104K63K31 TR12]	100 nF [MDC10104K50A52 P3TUBE]	100 nF [MDK10104K50A52 P3TUBE]
100 nF [C2220C104K1GACT U]	100 nF [GPC7.3104K63K37 TR12]	100 nF [MDC10104K630A5 8P7TUBE]	100 nF [MDK10104K630A5 8P7TUBE]
100 nF [C2220C104K2GACT U]	100 nF [LD166C104KAB2A]	100 nF [MDC10104K630A5 8P8TUBE]	100 nF [MDK10104K630A5 8P8TUBE]
100 nF [C2220C104K5GACT U]	100 nF [LD16ZC104KAB2A]	100 nF [MDC15104K100B5 3P3TUBE]	100 nF [MDK15104K250B5 3P3TUBE]
100 nF [C2225C104K1RACT U]	100 nF [LD173C104KAB2A]	100 nF [MDC15104K250B5 3P3TUBE]	100 nF [MDS10104K100A5 2P3TUBE]
100 nF [C2225C104K2RACT U]	100 nF [LD17YC104KAB2V]	100 nF [MDC15104K400B5 3P3TUBE]	100 nF [MDS10104K250A5 2P3TUBE]
100 nF [C2225C104K5RACT U]	100 nF [LD18ZC104KAB2S]	100 nF [MDC15104K50B53 P3TUBE]	100 nF [MDS10104K400A5 2P3TUBE]
100 nF [CA064C104K4RACT U]	100 nF [LG126D104MAT2S 1]	100 nF [MDC15104K630B5 3P3TUBE]	100 nF [MDS10104K50A52 P3TUBE]

Multisim 14.1 Base Edition Components

100 nF [MDS15104K100B5 3P3TUBE]	100 nF [PG224W104MAB2 S1]	100 nF [T494A104M050AT]	100 nH [SRP4012TA-R10Y]
100 nF [MDS15104K250B5 3P3TUBE]	100 nF [PG224Z104MAB2S 1]	100 nF [TAJA104K035RNJ]	100 nH [SRP4020TA-R10Y]
100 nF [MDS15104K630B5 3P3TUBE]	100 nF [PG226D104MAB2S 1]	100 nF [TAJA104K050RNJ]	100 nH [SRP7030- R10FM]
100 nF [MMC7.3104K100K 31TR12]	100 nF [PG226W104MAB2 S1]	100 nF [TAJR104K035RNJ]	100 nH [SRP8040- R10Y]
100 nF [PG124D104MAB2S 1]	100 nF [PG226Z104MAB2S 1]	100 nF [TAJS104K020RNJ]	100 Ohm [4108R-1- 101]
100 nF [PG124W104MAB2 S1]	100 nF [SPC10.2104K100A 31TR16]	100 nF [TAJS104K035RNJ]	100 Ohm [4108R-1- 101LF]
100 nF [PG124Z104MAB2S 1]	100 nF [SPC12.7104K250B 31TR24]	100 nF [THJA104K035RJN]	100 Ohm [4114R-1- 101]
100 nF [PG126D104MAB2S 1]	100 nF [SPC16.5104K400C 31TR24]	100 nF [TRJA104K035RRJ]	100 Ohm [4114R-2- 101LF]
100 nF [PG126W104MAB2 S1]	100 nF [SPC16.5104K630C 31TR24]	100 nF [W2L1YC104MAT1A]	100 Ohm [4116R-1- 101]
100 nF [PG126Z104MAB2S 1]	100 nF [T491A104M035AT]	100 nF [W3L1YC104MAT1A]	100 Ohm [4116R-1- 101LF]
100 nF [PG224D104MAB2S 1]	100 nF [T491A104M050AT]	100 nF [W3L1YC104MAT1S]	100 Ohm [4116R-2- 101LF]
	100 nF [T494A104M035AT]	100 nH [SRP1235- R10M]	100 Ohm [4304M- 102-101]

Multisim 14.1 Base Edition Components

100 Ohm [4304M-102-101LF]	100 Ohm [4308M-102-101LF]	100 Ohm [4311R-101-101]	100 Ohm [4604X-102-101LF]
100 Ohm [4306M-101-101]	100 Ohm [4308R-101-101]	100 Ohm [4416P-1-101]	100 Ohm [4604X-AP2-101LF]
100 Ohm [4306M-101-101LF]	100 Ohm [4308R-101-101LF]	100 Ohm [4416P-1-101LF]	100 Ohm [4605X-101-101LF]
100 Ohm [4306M-102-101]	100 Ohm [4308R-102-101]	100 Ohm [4416P-2-101]	100 Ohm [4606H-101-101LF]
100 Ohm [4306M-102-101LF]	100 Ohm [4308R-102-101LF]	100 Ohm [4416P-2-101LF]	100 Ohm [4606M-102-101LF]
100 Ohm [4306R-101-101]	100 Ohm [4309R-101-101]	100 Ohm [4416P-T01-101]	100 Ohm [4606X-101-101LF]
100 Ohm [4306R-101-101LF]	100 Ohm [4309R-101-101LF]	100 Ohm [4416P-T02-101]	100 Ohm [4606X-102-101LF]
100 Ohm [4306R-102-101]	100 Ohm [4310H-101-101]	100 Ohm [4420P-1-101]	100 Ohm [4606X-AP2-101LF]
100 Ohm [4306R-102-101LF]	100 Ohm [4310H-101-101LF]	100 Ohm [4420P-1-101LF]	100 Ohm [4607X-101-101LF]
100 Ohm [4308H-101-101]	100 Ohm [4310M-101-101]	100 Ohm [4420P-2-101]	100 Ohm [4608H-102-101LF]
100 Ohm [4308H-102-101]	100 Ohm [4310M-101-101LF]	100 Ohm [4420P-2-101LF]	100 Ohm [4608M-101-101LF]
100 Ohm [4308H-102-101LF]	100 Ohm [4310R-101-101]	100 Ohm [4420P-T01-101]	100 Ohm [4608M-102-101LF]
100 Ohm [4308M-101-101]	100 Ohm [4310R-101-101LF]	100 Ohm [4420P-T02-101]	100 Ohm [4608X-101-101LF]
100 Ohm [4308M-101-101LF]	100 Ohm [4310R-102-101]	100 Ohm [4420P-T04-101]	100 Ohm [4608X-102-101LF]
100 Ohm [4308M-102-101]	100 Ohm [4310R-102-101LF]	100 Ohm [4604X-101-101LF]	100 Ohm [4608X-AP1-101LF]

Multisim 14.1 Base Edition Components

100 Ohm [4608X-AP2-101LF]	100 Ohm [4614X-102-101LF]	100 Ohm [4816P-T01-101]	100 Ohm [CAT16-101J4GLF]
100 Ohm [4609H-101-101LF]	100 Ohm [4814P-1-101]	100 Ohm [4816P-T01-101LF]	100 Ohm [CAT16-101J4LF]
100 Ohm [4609M-101-101LF]	100 Ohm [4814P-1-101LF]	100 Ohm [4816P-T02-101]	100 Ohm [CAT16-101J8LF]
100 Ohm [4609X-101-101LF]	100 Ohm [4814P-2-101]	100 Ohm [4816P-T02-101LF]	100 Ohm [CAT25-101JALF]
100 Ohm [4610H-101-101LF]	100 Ohm [4814P-2-101LF]	100 Ohm [4818P-T02-101LF]	100 Ohm [CAY10-101J2LF]
100 Ohm [4610H-102-101LF]	100 Ohm [4814P-T01-101]	100 Ohm [4820P-1-101]	100 Ohm [CAY10-101J4LF]
100 Ohm [4610M-101-101LF]	100 Ohm [4814P-T01-101LF]	100 Ohm [4820P-1-101LF]	100 Ohm [CAY16-1000F4LF]
100 Ohm [4610M-102-101LF]	100 Ohm [4814P-T02-101]	100 Ohm [4820P-2-101]	100 Ohm [CAY16-101J2LF]
100 Ohm [4610X-101-101LF]	100 Ohm [4814P-T02-101LF]	100 Ohm [4820P-2-101LF]	100 Ohm [CAY16-101J4GLF]
100 Ohm [4610X-102-101LF]	100 Ohm [4816P-1-101]	100 Ohm [4820P-T01-101]	100 Ohm [CAY16-101J4LF]
100 Ohm [4610X-AP1-101LF]	100 Ohm [4816P-1-101F]	100 Ohm [4820P-T01-101LF]	100 Ohm [CAY16-101J8LF]
100 Ohm [4610X-AP2-101LF]	100 Ohm [4816P-1-101LF]	100 Ohm [4820P-T02-101]	100 Ohm [CAY17-101JALF]
100 Ohm [4611X-101-101LF]	100 Ohm [4816P-2-101]	100 Ohm [CAT10-101J4LF]	100 Ohm [CR0201-FW-1000GLF]
100 Ohm [4612X-102-101LF]	100 Ohm [4816P-2-101LF]	100 Ohm [CAT16-1000F4LF]	100 Ohm [CR0201-JW-101GLF]
100 Ohm [4613X-101-101LF]	100 Ohm [4816P-4-101]	100 Ohm [CAT16-101J2LF]	100 Ohm [CR0402-FX-1000GLF]

Multisim 14.1 Base Edition Components

100 Ohm [CR0402-JW-101GLF]	100 Ohm [CR2512-JW-101ELF]	100 Ohm [CRT0402-BY-1000GLF]	100 Ohm [CRT1206-DW-1000ELF]
100 Ohm [CR0603-FX-1000ELF]	100 Ohm [CRM1206-FX-1000ELF]	100 Ohm [CRT0402-BZ-1000GLF]	100 Ohm [CRT1206-FZ-1000ELF]
100 Ohm [CR0603-FX-1000HLF]	100 Ohm [CRM2010-FX-1000ELF]	100 Ohm [CRT0402-DY-1000GLF]	100 Ohm [CRT1206-PW-1000ELF]
100 Ohm [CR0603-JW-101ELF]	100 Ohm [CRM2512-FX-1000ELF]	100 Ohm [CRT0402-FZ-1000GLF]	100 Ohm [FW10A1000JA]
100 Ohm [CR0805-FX-1000ELF]	100 Ohm [CRM2512-JW-101ELF]	100 Ohm [CRT0603-BZ-1000ELF]	100 Ohm [FW20A1000JA]
100 Ohm [CR0805-JW-101ELF]	100 Ohm [CRS0805-FX-1000ELF]	100 Ohm [CRT0603-DY-1000ELF]	100 Ohm [FW30A1000JA]
100 Ohm [CR0805-JW-101GLF]	100 Ohm [CRS1206-FX-1000ELF]	100 Ohm [CRT0603-FY-1000ELF]	100 Ohm [FW50A1000JA]
100 Ohm [CR1206-FX-1000ELF]	100 Ohm [CRS1206-JX-101ELF]	100 Ohm [CRT0805-BY-1000ELF]	100 Ohm [FW70A1000JA]
100 Ohm [CR1206-FX-1000GLF]	100 Ohm [CRS2010-FX-1000ELF]	100 Ohm [CRT0805-BZ-1000ELF]	100 Ohm [PWR163S-25-1000F]
100 Ohm [CR1206-JW-101ELF]	100 Ohm [CRS2512-FX-1000ELF]	100 Ohm [CRT0805-CY-1000ELF]	100 Ohm [PWR163S-25-1000FE]
100 Ohm [CR2010-FX-1000ELF]	100 Ohm [CRT0402-BW-1000GLF]	100 Ohm [CRT0805-FX-1000ELF]	100 Ohm [PWR2010W1000JE]
100 Ohm [CR2010-JW-101ELF]			
100 Ohm [CR2512-FX-1000ELF]			

Multisim 14.1 Base Edition Components

100 Ohm [PWR220T-20-1000J]	100 Ohm [PWR263S-35-1000FE]	100 pF [C0201C101K3GACT U]	100 pF [C0603C101K5GACT U]
100 Ohm [PWR220T-35-1000J]	100 Ohm [PWR263S-35-1000J]	100 pF [C0402C101K1HACT U]	100 pF [C0603C101K5RACT U]
100 Ohm [PWR221T-30-1000F]	100 Ohm [PWR3014W1000JE]	100 pF [C0402C101K3GACT U]	100 pF [C0603C101K8GACT U]
100 Ohm [PWR221T-30-1000J]	100 Ohm [PWR4318W1000JE]	100 pF [C0402C101K3HACT U]	100 pF [C0805C101K1GACT U]
100 Ohm [PWR221T-50-1000J]	100 Ohm [PWR4525W1000J]	100 pF [C0402C101K4GACT U]	100 pF [C0805C101K2GACT U]
100 Ohm [PWR2615W1000F]	100 Ohm [PWR4525W1000JE]	100 pF [C0402C101K5GACT U]	100 pF [C0805C101K3GACT U]
100 Ohm [PWR2615W1000J]	100 Ohm [PWR5322W1000JE]	100 pF [C0402C101K5HACT U]	100 pF [C0805C101K4GACT U]
100 Ohm [PWR2615W1000JE]	100 Ohm [PWR6327W1000J]	100 pF [C0402C101K8GACT U]	100 pF [C0805C101K5GACT U]
100 Ohm [PWR263S-20-1000F]	100 Ohm [PWR6327W1000JE]	100 pF [C0603C101K1GACT U]	100 pF [C0805C101KBGAC TU]
100 Ohm [PWR263S-20-1000FE]	100 Ohm [W1M1000J]	100 pF [C0603C101K3GACT U]	100 pF [C0805C101KCGAC TU]
100 Ohm [PWR263S-20-1000J]	100 pF [03028BR101AKZC]	100 pF [C0603C101K4GACT U]	100 pF [C0805C101KDGAC TU]
100 Ohm [PWR263S-35-1000F]			

Multisim 14.1 Base Edition Components

100 pF [C0805H101K5GAC TU]	100 pF [C1210C101KCGAC TU]	100 pF [CA064C101K8GAC TU]	100 uF [6TPE100MI]
100 pF [C1206C101K1GACT U]	100 pF [C1210C101KDGAC TU]	100 pF [W2F11A1018AT1A]	100 uF [6TPE100MPB]
100 pF [C1206C101K2GACT U]	100 pF [C1812C101KBGAC TU]	100 pF [W3F11A1018AT1A]	100 uF [6TPG100M]
100 pF [C1206C101K3GACT U]	100 pF [C1812C101KDGAC TU]	100 uF [10TPC100M]	100 uF [6TPH100MABC]
100 pF [C1206C101K5GACT U]	100 pF [C1812C101KHGAC TU]	100 uF [16SEPC100M]	100 uF [6TPH100MAEA]
100 pF [C1206C101KBGAC TU]	100 pF [C1825C101KBGAC TU]	100 uF [16TQC100MYF]	100 uF [A700D107M006AT E015]
100 pF [C1206C101KCGAC TU]	100 pF [C2220C101KBGAC TU]	100 uF [20SVP100M]	100 uF [A700D107M006AT E018]
100 pF [C1206C101KDGAC TU]	100 pF [C2225C101KBGAC TU]	100 uF [20TQC100MYF]	100 uF [A700V107M002AT E018]
100 pF [C1206C101KGGAC TU]	100 pF [CA064C101K1GAC TU]	100 uF [6SVPC100M]	100 uF [A700V107M002AT E025]
100 pF [C1210C101K5GACT U]	100 pF [CA064C101K3GAC TU]	100 uF [6SVPC100MY]	100 uF [A700V107M002AT E028]
100 pF [C1210C101KBGAC TU]	100 pF [CA064C101K5GAC TU]	100 uF [6TPE100M]	100 uF [A700X107M008AT E010]
		100 uF [6TPE100MAZB]	

Multisim 14.1 Base Edition Components

100 uF [A700X107M008AT E015]	100 uF [T489C107M010AT E500]	100 uF [T491D107M016AT]	100 uF [T494B107M004AT]
100 uF [A700X107M010AT E010]	100 uF [T489D107M010AT E150]	100 uF [T491D107M020AT]	100 uF [T494B107M006AT]
100 uF [A700X107M010AT E015]	100 uF [T489D107M010AT E440]	100 uF [T491E107M020AT]	100 uF [T494C107M006AT]
100 uF [EEFCT0J101R]	100 uF [T491A107M004AT]	100 uF [T491T107M004AT]	100 uF [T494C107M010AT]
100 uF [EEFCX0J101R]	100 uF [T491B107M004AT]	100 uF [T491T107M2R5AT]	100 uF [T494D107M004AT]
100 uF [EEFCX1A101R]	100 uF [T491B107M006AT]	100 uF [T491U107M004AT]	100 uF [T494D107M006AT]
100 uF [EEFHX1A101R]	100 uF [T491B107M010AT]	100 uF [T491U107M006AT]	100 uF [T494D107M010AT]
100 uF [EEFSX0G101ER]	100 uF [T491C107M004AT]	100 uF [T491V107M006AT]	100 uF [T494D107M016AT]
100 uF [EEHZA1E101XP]	100 uF [T491C107M006AT]	100 uF [T491V107M010AT]	100 uF [T494E107M020AT]
100 uF [EEHZA1H101P]	100 uF [T491C107M010AT]	100 uF [T491V107M016AT]	100 uF [T494T107M004AT]
100 uF [EEHZC1E101XP]	100 uF [T491D107M004AT]	100 uF [T491X107M016AT]	100 uF [T494T107M2R5AT]
100 uF [EEHZC1H101P]	100 uF [T491D107M006AT]	100 uF [T491X107M020AT]	100 uF [T494U107M004AT]
100 uF [ETPH100MHA]	100 uF [T491D107M010AT]	100 uF [T491X107M025AT]	
100 uF [ETPU100MSI]		100 uF [T494A107M004AT]	

Multisim 14.1 Base Edition Components

100 uF [T494U107M006AT]	100 uF [T495D107M010AT E050]	100 uF [T495V107M010AT E150]	100 uF [T513D107M016AH 6110]
100 uF [T494V107M006AT]	100 uF [T495D107M010AT E065]	100 uF [T495X107M010AT E100]	100 uF [T513E107M025AH 6110]
100 uF [T494V107M010AT]	100 uF [T495D107M010AT E080]	100 uF [T495X107M016AT E080]	100 uF [T513X107M020AH 6110]
100 uF [T494V107M016AT]			
100 uF [T494X107M016AT]	100 uF [T495D107M010AT E100]	100 uF [T495X107M016AT E100]	100 uF [T513X107M020AH 6120]
100 uF [T494X107M020AT]	100 uF [T495D107M016AT E100]	100 uF [T495X107M020AT E100]	100 uF [T520B107M003AT E035]
100 uF [T494X107M025AT]	100 uF [T495D107M016AT E125]	100 uF [T495X107M020AT E150]	100 uF [T520B107M003AT E040]
100 uF [T495B107M006AT E400]	100 uF [T495E107M020AT E060]	100 uF [T498D107M006AT E600]	100 uF [T520B107M003AT E070]
100 uF [T495B107M006AT E700]	100 uF [T495E107M020AT E200]	100 uF [T498D107M010AT E600]	100 uF [T520B107M004AT E035]
100 uF [T495B107M010AT E350]	100 uF [T495T107M2R5AT E3K0]	100 uF [T510E107M025AT E050]	100 uF [T520B107M004AT E040]
100 uF [T495C107M006AT E150]	100 uF [T495V107M006AT E150]	100 uF [T510X107M020AT E040]	100 uF [T520B107M004AT E070]
100 uF [T495D107M006AT E050]	100 uF [T495V107M010AT E100]	100 uF [T510X107M020AT E045]	100 uF [T520B107M006AT E015]
100 uF [T495D107M006AT E130]			

Multisim 14.1 Base Edition Components

100 uF [T520B107M006AT E018]	100 uF [T520D107M006AT E007]	100 uF [T520V107M006AT E009]	100 uF [T521X107M025AT E060]
100 uF [T520B107M006AT E025]	100 uF [T520D107M010AT E018]	100 uF [T520V107M006AT E012]	100 uF [T525B107M003AT E080]
100 uF [T520B107M006AT E035]	100 uF [T520D107M010AT E055]	100 uF [T520V107M006AT E045]	100 uF [T525B107M004AT E080]
100 uF [T520B107M006AT E040]	100 uF [T520D107M010AT E080]	100 uF [T520V107M010AT E018]	100 uF [T525D107M010AT E025]
100 uF [T520B107M006AT E070]	100 uF [T520T107M004AT E070]	100 uF [T520V107M010AT E025]	100 uF [T525D107M010AT E055]
100 uF [T520B107M2R5AT E035]	100 uF [T520T107M004AT E150]	100 uF [T520V107M010AT E045]	100 uF [T525T107M2R5AT E080]
100 uF [T520B107M2R5AT E040]	100 uF [T520T107M006AT E070]	100 uF [T520V107M010AT E050]	100 uF [T528I107M003ATE 200]
100 uF [T520C107M006AT E025]	100 uF [T520T107M2R5AT E070]	100 uF [T520W107M006AT E040]	100 uF [T540B107M004AH 6510]
100 uF [T520C107M006AT E045]	100 uF [T520U107M004AT E055]	100 uF [T520W107M010AT E040]	100 uF [T540D107M010AH 6510]
100 uF [T520C107M010AT E025]	100 uF [T520U107M006AT E055]	100 uF [T521D107M016AT E050]	100 uF [TAJA107K004RNJ]
100 uF [T520C107M010AT E045]	100 uF [T520V107M006AT E007]	100 uF [T521V107M016AT E050]	100 uF [TAJB107K004RNJ]
			100 uF [TAJB107K006RNJ]

Multisim 14.1 Base Edition Components

100 uF [TAJC107K006RNJ]	100 uF [TAJX107K010RNJ]	100 uF [TPSC107K006R015 0]	100 uF [TPSD107K010R012 5]
100 uF [TAJC107K010RNJ]	100 uF [TAJY107K006RNJ]	100 uF [TPSC107K010R007 5]	100 uF [TPSD107K010R015 0]
100 uF [TAJC107K016RNJ]	100 uF [TAJY107K010RNJ]	100 uF [TPSC107K010R010 0]	100 uF [TPSD107K016R006 0]
100 uF [TAJD107K010RNJ]	100 uF [THJD107K010RJN]	100 uF [TPSC107K010R015 0]	100 uF [TPSD107K016R010 0]
100 uF [TAJD107K016RNJ]	100 uF [THJE107K016RJN]	100 uF [TPSC107K010R020 0]	100 uF [TPSD107K016R012 5]
100 uF [TAJD107K020RNJ]	100 uF [TPME107K020R00 35]	100 uF [TPSC107K016R020 0]	100 uF [TPSD107K016R015 0]
100 uF [TAJE107K010RNJ]	100 uF [TPME107K020R00 45]	100 uF [TPSD107K006R030 0]	100 uF [TPSD107K020R008 5]
100 uF [TAJE107K016RNJ]	100 uF [TPSB107K004R035 0]	100 uF [TPSD107K010R005 0]	100 uF [TPSD107K020R010 0]
100 uF [TAJE107K020RNJ]	100 uF [TPSB107K004R050 0]	100 uF [TPSD107K010R006 5]	100 uF [TPSD107K020R015 0]
100 uF [TAJT107K002RNJ]	100 uF [TPSB107K006R025 0]	100 uF [TPSD107K010R008 0]	100 uF [TPSE107K010R012 5]
100 uF [TAJV107K020RNJ]	100 uF [TPSB107K006R040 0]	100 uF [TPSD107K010R010 0]	100 uF [TPSE107K016R005 5]
100 uF [TAJW107K004RNJ]	100 uF [TPSC107K006R007 5]		
100 uF [TAJW107K006RNJ]			
100 uF [TAJW107K010RNJ]			

Multisim 14.1 Base Edition Components

100 uF [TPSE107K016R010 0]	100 uF [TPSY107K006R010 0]	100 uH [SDE1006A- 101K]	100 uH [SDR1307- 101KL]
100 uF [TPSE107K016R012 5]	100 uF [TPSY107K010R010 0]	100 uH [SDR0302- 101KL]	100 uH [SDR1307A-101K]
100 uF [TPSE107K016R015 0]	100 uF [TPSY107K010R015 0]	100 uH [SDR0503- 101KL]	100 uH [SDR6603- 101M]
100 uF [TPSE107K020R015 0]	100 uF [TPSY107K010R020 0]	100 uH [SDR0603- 101KL]	100 uH [SDR7030- 101K]
100 uF [TPSE107K020R020 0]	100 uF [TPSY107K016R010 0]	100 uH [SDR0604- 101KL]	100 uH [SDR7045- 101K]
100 uF [TPSV107K020R006 0]	100 uF [TPSY107K016R015 0]	100 uH [SDR0703- 101KL]	100 uH [SRN1060- 101M]
100 uF [TPSV107K020R008 5]	100 uF [TPSY107K016R020 0]	100 uH [SDR0805- 101KL]	100 uH [SRN3015- 101M]
100 uF [TPSV107K020R010 0]	100 uF [TRJD107K010RRJ]	100 uH [SDR0906- 101KL]	100 uH [SRN4018- 101M]
100 uF [TPSV107K020R020 0]	100 uF [TRJD107K016RRJ]	100 uH [SDR1005- 101KL]	100 uH [SRN4026- 101M]
100 uF [TPSX107K010R015 0]	100 uF [TRJE107K016RRJ]	100 uH [SDR1006- 101KL]	100 uH [SRN6028- 101M]
100 uF [TPSX107K010R020 0]	100 uH [SDE0604A- 101K]	100 uH [SDR1030- 101K]	100 uH [SRN6045- 101M]
	100 uH [SDE0805A- 101K]	100 uH [SDR1045- 101K]	100 uH [SRN8040- 101M]
		100 uH [SDR1105- 101KL]	100 uH [SRP1770TA-101M]
		100 uH [SDR1305- 101K]	100 uH [SRR0603- 101KL]

Multisim 14.1 Base Edition Components

100 uH [SRR0604-101KL]	100 uH [SRR1210A-101M]	100 uH [SRR6603-101ML]	100 uH [SRU5028-101Y]
100 uH [SRR0618-101ML]	100 uH [SRR1240-101M]	100 uH [SRR7032-101M]	100 uH [SRU5028A-101Y]
100 uH [SRR0735A-101M]	100 uH [SRR1260-101M]	100 uH [SRR7045-101M]	100 uH [SRU6018-101Y]
100 uH [SRR0745A-101M]	100 uH [SRR1260A-101M]	100 uH [SRU1028-101Y]	100 uH [SRU6025-101Y]
100 uH [SRR0804-101K]	100 uH [SRR1280-101M]	100 uH [SRU1028A-101Y]	100 uH [SRU6025A-101Y]
100 uH [SRR0805-101K]	100 uH [SRR1806-101M]	100 uH [SRU1038-101Y]	100 uH [SRU8028-101Y]
100 uH [SRR0905-101K]	100 uH [SRR3011-101YL]	100 uH [SRU1038A-101Y]	100 uH [SRU8028A-101Y]
100 uH [SRR0906-101YL]	100 uH [SRR4011-101YL]	100 uH [SRU1048-101Y]	100 uH [SRU8043-101Y]
100 uH [SRR0908-101YL]	100 uH [SRR4018-101Y]	100 uH [SRU1048A-101Y]	10029449-001RLF
100 uH [SRR1003-101M]	100 uH [SRR4028-101Y]	100 uH [SRU1063-101Y]	100V_100W
100 uH [SRR1005-101K]	100 uH [SRR5018-101Y]	100 uH [SRU2016-101Y]	10104111-0001LF
100 uH [SRR1205-101KL]	100 uH [SRR5028-101Y]	100 uH [SRU3028-101Y]	102 kOhm [CR0201-FW-1023GLF]
100 uH [SRR1206-101YL]	100 uH [SRR6028-101Y]	100 uH [SRU5011-101Y]	102 kOhm [CR0402-FX-1023GLF]
100 uH [SRR1208-101YL]	100 uH [SRR6038-101Y]	100 uH [SRU5016-101Y]	102 kOhm [CR0603-FX-1023ELF]
100 uH [SRR1210-101M]	100 uH [SRR6040A-101M]	100 uH [SRU5018-101Y]	102 kOhm [CR0805-FX-1023ELF]

Multisim 14.1 Base Edition Components

102 kOhm [CR1206-FX-1023ELF]	105 Ohm [CR0402-FX-1050GLF]	10Line_Bussed	11 kOhm [CR1206-JW-113ELF]
102 kOhm [CRT0603-BX-1023ELF]	105 Ohm [CR0603-FX-1050ELF]	10Line_Isolated	11 kOhm [CR2010-JW-113ELF]
102 kOhm [CRT0805-BW-1023ELF]	105 Ohm [CR0603-FX-1050GLF]	11 kOhm [4116R-1-113]	11 kOhm [CRM2512-FX-1102ELF]
102 Ohm [CR0402-FX-1020GLF]	105 Ohm [CR0805-FX-1050ELF]	11 kOhm [CAT16-1102F4LF]	11 kOhm [CRT0402-BY-1102GLF]
102 Ohm [CR0603-FX-1020ELF]	105 Ohm [CR1206-FX-1050ELF]	11 kOhm [CAT16-113J4LF]	11 kOhm [CRT0603-BY-1102ELF]
102 Ohm [CR0805-FX-1020ELF]	105 Ohm [CRM2512-FX-1050ELF]	11 kOhm [CAY16-1102F4LF]	11 kOhm [CRT0603-BZ-1102ELF]
102 Ohm [CR1206-FX-1020ELF]	105081-0001	11 kOhm [CAY16-113J4LF]	11 kOhm [CRT0805-BW-1102ELF]
1028	107 kOhm [CR0603-FX-1073ELF]	11 kOhm [CR0201-FW-1102GLF]	11 kOhm [CRT0805-DZ-1102ELF]
105 kOhm [CR0402-FX-1053GLF]	107 kOhm [CR0805-FX-1073ELF]	11 kOhm [CR0402-FX-1102GLF]	11 kOhm [CRT1206-BY-1102ELF]
105 kOhm [CR0603-FX-1053ELF]	107 kOhm [CR1206-FX-1073ELF]	11 kOhm [CR0402-JW-113GLF]	11 MOhm [4604X-102-116LF]
105 kOhm [CR0805-FX-1053ELF]	107 kOhm [CRT0402-BY-1073GLF]	11 kOhm [CR0603-FX-1102ELF]	11 Ohm [CAY16-110J4LF]
105 kOhm [CR1206-FX-1053ELF]	107 Ohm [CR0603-FX-1070ELF]	11 kOhm [CR0603-JW-113ELF]	11 Ohm [CR0402-FX-11R0GLF]
105 kOhm [CRT0603-BY-1053ELF]	107 Ohm [CR0805-FX-1070ELF]	11 kOhm [CR0805-FX-1102ELF]	11 Ohm [CR0603-FX-11R0ELF]
	107 Ohm [CR1206-FX-1070ELF]	11 kOhm [CR1206-FX-1102ELF]	

Multisim 14.1 Base Edition Components

11 Ohm [CR0603-JW-110ELF]	11 pF [C1206C110KBGAC TU]	11.3 kOhm [CRT0805-DZ-1132ELF]	11.5 Ohm [CR0805-FX-11R5ELF]
11 Ohm [CR0805-FX-11R0ELF]	11 pF [C1210C110KBGAC TU]	11.3 Ohm [CR0201-FW-11R3GLF]	11.5 Ohm [CR1206-FX-11R5ELF]
11 Ohm [CR0805-FX-11R0GLF]	11 pF [C1812C110KBGAC TU]	11.3 Ohm [CR0805-FX-11R3ELF]	11.5 Ohm [CRT0402-FZ-11R5GLF]
11 Ohm [CR0805-JW-110ELF]	11 pF [C1825C110KBGAC TU]	11.5 kOhm [CR0402-FX-1152GLF]	11.5 Ohm [CRT0805-BY-11R5ELF]
11 Ohm [CR1206-FX-11R0ELF]	11 pF [C2220C110KBGAC TU]	11.5 kOhm [CR0603-FX-1152ELF]	11.5 Ohm [CRT1206-BW-11R5ELF]
11 Ohm [CR1206-JW-110ELF]	11 pF [C2225C110KBGAC TU]	11.5 kOhm [CR0805-FX-1152ELF]	11.8 kOhm [CR0402-FX-1182GLF]
11 Ohm [CRM2512-FX-11R0ELF]	11.3 kOhm [CR0402-FX-1132GLF]	11.5 kOhm [CR0805-FX-1152GLF]	11.8 kOhm [CR0603-FX-1182ELF]
11 Ohm [CRT0805-BW-11R0ELF]	11.3 kOhm [CR0603-FX-1132ELF]	11.5 kOhm [CR1206-FX-1152ELF]	11.8 kOhm [CR0805-FX-1182ELF]
11 Ohm [CRT0805-BY-11R0ELF]	11.3 kOhm [CR0805-FX-1132ELF]	11.5 kOhm [CRT0402-FZ-1152GLF]	11.8 kOhm [CR1206-FX-1182ELF]
11 Ohm [CRT1206-CW-11R0ELF]	11.3 kOhm [CR1206-FX-1132ELF]	11.5 Ohm [CR0402-FX-11R5GLF]	11.8 Ohm [CR0603-FX-11R8ELF]
11 Ohm [PWR4525W11R0FE]	11.3 kOhm [CRT0805-BY-1132ELF]	11.5 Ohm [CR0603-FX-11R5ELF]	11.8 Ohm [CR0805-FX-11R8ELF]
11 Ohm [PWR6327N11R0FE]			11.8 Ohm [CR1206-FX-11R8ELF]
11 pF [C0805C110KBGAC TU]			110 kOhm [4116R-1-114]

Multisim 14.1 Base Edition Components

110 kOhm [4606X-AP1-114LF]	110 kOhm [CRM2512-FX-1103ELF]	110 mOhm [CRL2010-JW-R110ELF]	110 Ohm [4816P-2-111]
110 kOhm [4610X-101-114LF]	110 kOhm [CRT0402-BY-1103GLF]	110 mOhm [CRL2512-FW-R110ELF]	110 Ohm [4816P-2-111LF]
110 kOhm [CAY16-114J4LF]	110 kOhm [CRT0603-BY-1103ELF]	110 Ohm [4116R-1-111]	110 Ohm [4816P-T02-111]
110 kOhm [CR0402-FX-1103GLF]	110 kOhm [CRT0603-FW-1103ELF]	110 Ohm [4116R-1-111LF]	110 Ohm [4820P-2-111F]
110 kOhm [CR0402-JW-114GLF]	110 mOhm [CRL0603-FW-R110ELF]	110 Ohm [4306R-101-111]	110 Ohm [CAT16-1100F4LF]
110 kOhm [CR0603-FX-1103ELF]	110 mOhm [CRL0603-JW-R110ELF]	110 Ohm [4308R-102-111]	110 Ohm [CAT16-111J4LF]
110 kOhm [CR0603-FX-1103GLF]	110 mOhm [CRL0805-FW-R110ELF]	110 Ohm [4308R-102-111LF]	110 Ohm [CAY16-1100F4LF]
110 kOhm [CR0603-JW-114ELF]	110 mOhm [CRL0805-JW-R110ELF]	110 Ohm [4310R-101-111]	110 Ohm [CAY16-111J4LF]
110 kOhm [CR0805-FX-1103ELF]	110 mOhm [CRL1206-FW-R110ELF]	110 Ohm [4310R-101-111LF]	110 Ohm [CR0402-FX-1100GLF]
110 kOhm [CR0805-JW-114ELF]	110 mOhm [CRL1206-JW-R110ELF]	110 Ohm [4608X-101-111LF]	110 Ohm [CR0402-JW-111GLF]
110 kOhm [CR1206-FX-1103ELF]	110 mOhm [CRL2010-FW-R110ELF]	110 Ohm [4610X-101-111LF]	110 Ohm [CR0603-FX-1100ELF]
110 kOhm [CR1206-JW-114ELF]		110 Ohm [4610X-102-111LF]	110 Ohm [CR0603-JW-111ELF]
		110 Ohm [4816P-1-111]	110 Ohm [CR0805-FX-1100ELF]
		110 Ohm [4816P-1-111LF]	110 Ohm [CR0805-JW-111ELF]

Multisim 14.1 Base Edition Components

110 Ohm [CR1206-FX-1100ELF]	110 pF [C0805C111K1GACT U]	113 kOhm [CR1206-FX-1133ELF]	115 Ohm [CR1206-FX-1150ELF]
110 Ohm [CR1206-FX-1100GLF]	110 pF [C1206C111K5GACT U]	113 Ohm [CR0603-FX-1130ELF]	115 Ohm [CRT0805-BY-1150ELF]
110 Ohm [CR1206-JW-111ELF]	110 pF [C1206C111KBGACT TU]	113 Ohm [CR0805-FX-1130ELF]	118 kOhm [CR0402-FX-1183GLF]
110 Ohm [CR2512-FX-1100ELF]	110 pF [C1210C111KBGACT TU]	113 Ohm [CR1206-FX-1130ELF]	118 kOhm [CR0603-FX-1183ELF]
110 Ohm [CR2512-JW-111ELF]	110 pF [C1812C111KBGACT TU]	115 kOhm [CR0402-FX-1153GLF]	118 kOhm [CR0805-FX-1183ELF]
110 Ohm [CRT0402-FZ-1100GLF]	110 pF [C1825C111KBGACT TU]	115 kOhm [CR0603-FX-1153ELF]	118 kOhm [CR1206-FX-1183ELF]
110 Ohm [CRT1206-BW-1100ELF]	110 pF [C2220C111KBGACT TU]	115 kOhm [CR0805-FX-1153ELF]	118 Ohm [CR0402-FX-1180GLF]
110 Ohm [PWR220T-35-1100J]	110 pF [C2225C111KBGACT TU]	115 kOhm [CR1206-FX-1153ELF]	118 Ohm [CR0603-FX-1180ELF]
110 pF [C0402C111K1HACT U]	113 kOhm [CR0402-FX-1133GLF]	115 kOhm [CRT0805-BY-1153ELF]	118 Ohm [CR0805-FX-1180ELF]
110 pF [C0402C111K3HACT U]	113 kOhm [CR0603-FX-1133ELF]	115 kOhm [CRT0805-FW-1153ELF]	118 Ohm [CR1206-FX-1180ELF]
110 pF [C0402C111K5HACT U]	113 kOhm [CR0805-FX-1133ELF]	115 Ohm [CR0402-FX-1150GLF]	118 Ohm [CRS1206-FX-1180ELF]
110 pF [C0603C111K5GACT U]		115 Ohm [CR0603-FX-1150ELF]	12 kOhm [4108R-1-123LF]
		115 Ohm [CR0805-FX-1150ELF]	12 kOhm [4114R-1-123]

Multisim 14.1 Base Edition Components

12 kOhm [4114R-1-123LF]	12 kOhm [4308R-102-123LF]	12 kOhm [4608H-102-123LF]	12 kOhm [4816P-1-123LF]
12 kOhm [4114R-2-123]	12 kOhm [4309R-101-123LF]	12 kOhm [4608X-101-123LF]	12 kOhm [4816P-2-123]
12 kOhm [4116R-1-123]	12 kOhm [4310H-101-123]	12 kOhm [4608X-102-123LF]	12 kOhm [4816P-2-123LF]
12 kOhm [4116R-1-123LF]	12 kOhm [4310M-101-123]	12 kOhm [4609X-101-123LF]	12 kOhm [4816P-T01-123]
12 kOhm [4116R-2-123]	12 kOhm [4310M-101-123LF]	12 kOhm [4610H-101-123LF]	12 kOhm [4816P-T01-123LF]
12 kOhm [4116R-2-123LF]	12 kOhm [4310R-101-123]	12 kOhm [4610H-102-123LF]	12 kOhm [4816P-T02-123]
12 kOhm [4306H-101-123]	12 kOhm [4310R-101-123LF]	12 kOhm [4610M-101-123LF]	12 kOhm [4816P-T02-123LF]
12 kOhm [4306H-101-123LF]	12 kOhm [4310R-102-123]	12 kOhm [4610X-101-123LF]	12 kOhm [4820P-2-123F]
12 kOhm [4306R-101-123]	12 kOhm [4310R-102-123LF]	12 kOhm [4610X-102-123LF]	12 kOhm [CAT16-1202F4LF]
12 kOhm [4306R-101-123LF]	12 kOhm [4604X-101-123LF]	12 kOhm [4610X-AP2-123LF]	12 kOhm [CAT16-123J4LF]
12 kOhm [4306R-102-123]	12 kOhm [4604X-102-123LF]	12 kOhm [4611X-101-123LF]	12 kOhm [CAT25-123JALF]
12 kOhm [4306R-102-123LF]	12 kOhm [4605X-101-123LF]	12 kOhm [4612X-102-123LF]	12 kOhm [CAY16-1202F4LF]
12 kOhm [4308R-101-123]	12 kOhm [4606X-101-123LF]	12 kOhm [4814P-2-123]	12 kOhm [CAY16-123J4LF]
12 kOhm [4308R-101-123LF]	12 kOhm [4606X-102-123LF]	12 kOhm [4814P-T02-123]	12 kOhm [CAY16-123J8LF]
12 kOhm [4308R-102-123]	12 kOhm [4607X-101-123LF]	12 kOhm [4816P-1-123]	12 kOhm [CAY17-123JALF]

Multisim 14.1 Base Edition Components

12 kOhm [CR0402-FX-1202GLF]	12 kOhm [CRT0805-BW-1202ELF]	12 nF [C0402C123K9RACTU]	12 nF [C0805C123K5GACTU]
12 kOhm [CR0402-JW-123GLF]	12 kOhm [CRT0805-BY-1202ELF]	12 nF [C0603C123K1RACTU]	12 nF [C0805C123K5HACTU]
12 kOhm [CR0603-FX-1202ELF]	12 kOhm [CRT0805-FX-1202ELF]	12 nF [C0603C123K3RACTU]	12 nF [C0805C123K5RACTU]
12 kOhm [CR0805-FX-1202ELF]	12 kOhm [PWR4525W1202JE]	12 nF [C0603C123K4RACTU]	12 nF [C0805C123K8RACTU]
12 kOhm [CR0805-JW-123ELF]	12 mH [SDR0503-123JL]	12 nF [C0603C123K5RACTU]	12 nF [C0805C123KARACTU]
12 kOhm [CR1206-FX-1202ELF]	12 mOhm [CRF2512-FZ-R012ELF]	12 nF [C0805C123K1GACTU]	12 nF [C0805F123K1RACTU]
12 kOhm [CR1206-JW-123ELF]	12 nF [C0402C123K4RACTU]	12 nF [C0805C123K1HACTU]	12 nF [C0805F123K3RACTU]
12 kOhm [CR2512-JW-123ELF]	12 nF [C0402C123K5RACTU]	12 nF [C0805C123K1RACTU]	12 nF [C0805F123K4RACTU]
12 kOhm [CRM1206-JW-123ELF]	12 nF [C0402C123K8PACTU]	12 nF [C0805C123K3HACTU]	12 nF [C0805F123K5RACTU]
12 kOhm [CRT0402-BY-1202GLF]	12 nF [C0402C123K8RACTU]	12 nF [C0805C123K3RACTU]	12 nF [C1206C123K1HACTU]
12 kOhm [CRT0603-BW-1202ELF]	12 nF [C0402C123K9PACTU]	12 nF [C0805C123K4RACTU]	12 nF [C1206C123K1RACTU]
12 kOhm [CRT0603-BY-1202ELF]			

Multisim 14.1 Base Edition Components

12 nF [C1206C123K2RACT U]	12 nF [C1210C123K5RACT U]	12 nF [MMC5.7123K250J 31TR12]	12 Ohm [CAY16- 120J4LF]
12 nF [C1206C123K3HACT U]	12 nF [C1210C123KARACT U]	12 nF [MMC7.3123K400K 35TR12]	12 Ohm [CAY16- 120J8LF]
12 nF [C1206C123K5HACT U]	12 nF [C1812C123K1RACT U]	12 Ohm [4116R-1- 120]	12 Ohm [CR0402- FX-12R0GLF]
12 nF [C1206C123K5RACT U]	12 nF [C2220C123K2GACT U]	12 Ohm [4116R-1- 120LF]	12 Ohm [CR0603- FX-12R0ELF]
12 nF [C1206C123KARACT U]	12 nF [GMC5.7122K250J3 1TR12]	12 Ohm [4306R- 102-120LF]	12 Ohm [CR0603- JW-120ELF]
12 nF [C1210C123K1GACT U]	12 nF [GMC5.7123K100J3 1TR12]	12 Ohm [4308R- 102-120]	12 Ohm [CR0805- FX-12R0ELF]
12 nF [C1210C123K1HACT U]	12 nF [GMC5.7123K50J31 TR12]	12 Ohm [4308R- 102-120LF]	12 Ohm [CR0805- FX-12R0GLF]
12 nF [C1210C123K3HACT U]	12 nF [GMC7.3122K250K3 1TR12]	12 Ohm [4420P- T02-120LF]	12 Ohm [CR0805- JW-120ELF]
12 nF [C1210C123K4RACT U]	12 nF [GMC7.3122K63K31 TR12]	12 Ohm [4606X- 102-120LF]	12 Ohm [CR1206- FX-12R0ELF]
12 nF [C1210C123K5GACT U]	12 nF [GMC7.3123K250K3 1TR12]	12 Ohm [4608X- 102-120LF]	12 Ohm [CR1206- JW-120ELF]
12 nF [C1210C123K5HACT U]	12 nF [GMC7.3123K63K31 TR12]	12 Ohm [4610X- 102-120LF]	12 Ohm [CRM1206-FX- 12R0ELF]
		12 Ohm [4816P-1- 120]	12 Ohm [CRM2512-FX- 12R0ELF]
		12 Ohm [CAT16- 120J2LF]	12 Ohm [CRM2512-JW- 120ELF]
		12 Ohm [CAT16- 120J4LF]	
		12 Ohm [CAT25- 120JALF]	

Multisim 14.1 Base Edition Components

12 Ohm [CRT0603-FY-12R0ELF]	12 pF [C0201C120K3GACT U]	12 pF [C1206C120K5GACT U]	12 uH [SDE0403A-120M]
12 Ohm [CRT1206-BY-12R0ELF]	12 pF [C0402C120K4GACT U]	12 pF [C1206C120KBGAC TU]	12 uH [SDE0604A-120M]
12 Ohm [PWR163S-25-12R0F]	12 pF [C0402C120K5GACT U]	12 pF [C1210C120KBGAC TU]	12 uH [SDE0805A-120M]
12 Ohm [PWR163S-25-12R0J]	12 pF [C0603C120K1GACT U]	12 pF [C1812C120KBGAC TU]	12 uH [SDE1006A-120M]
12 Ohm [PWR220T-20-12R0F]	12 pF [C0603C120K2GACT U]	12 pF [C1825C120KBGAC TU]	12 uH [SDR0302-120ML]
12 Ohm [PWR220T-20-12R0J]	12 pF [C0603C120K3GACT U]	12 pF [C2220C120KBGAC TU]	12 uH [SDR0403-120ML]
12 Ohm [PWR221T-30-12R0F]	12 pF [C0603C120K5GACT U]	12 pF [C2225C120KBGAC TU]	12 uH [SDR0503-120ML]
12 Ohm [PWR263S-20-12R0F]	12 pF [C0805C120K1GACT U]	12 pF [CA064C120K5GAC TU]	12 uH [SDR0603-120ML]
12 Ohm [PWR263S-20-12R0J]	12 pF [C0805C120K5GACT U]	12 uF [C1210C126K8PACT U]	12 uH [SDR0604-120ML]
12 Ohm [PWR263S-20-12R0JE]	12 pF [C0805C120KBGAC TU]	12 uF [MDC10126K50A58 P7TUBE]	12 uH [SDR0703-120KL]
12 Ohm [PWR263S-35-12R0F]	12 pF [C1206C120K1GACT U]	12 uF [MDC10126K50A58 P8TUBE]	12 uH [SDR0805-120ML]
12 Ohm [PWR263S-35-12R0J]			12 uH [SDR0906-120ML]
			12 uH [SDR1006-120ML]
			12 uH [SDR1105-120ML]
			12 uH [SDR1307-120ML]

Multisim 14.1 Base Edition Components

12 uH [SDR1307A-120M]	12 uH [SRR1240-120M]	12 uH [SRU8043-120Y]	12.1 Ohm [CR0805-FX-12R1ELF]
12 uH [SRR0735A-120M]	12 uH [SRR1260-120M]	12.1 kOhm [CR0402-FX-1212GLF]	12.1 Ohm [CR0805-FX-12R1GLF]
12 uH [SRR0745A-120M]	12 uH [SRR1260A-120M]	12.1 kOhm [CR0603-FX-1212ELF]	12.1 Ohm [CR1206-FX-12R1ELF]
12 uH [SRR0804-120M]	12 uH [SRR1280-120M]	12.1 kOhm [CR0805-FX-1212ELF]	12.1 Ohm [CRM1206-FX-12R1ELF]
12 uH [SRR0805-120M]	12 uH [SRR4018-120Y]	12.1 kOhm [CR1206-FX-1212ELF]	12.1 Ohm [CRM2512-FX-12R1ELF]
12 uH [SRR0905-120M]	12 uH [SRR4028-120Y]	12.1 kOhm [CRT0402-FZ-1212GLF]	12.1 Ohm [CRT0402-FZ-12R1GLF]
12 uH [SRR0906-120ML]	12 uH [SRR5018-120Y]	12.1 kOhm [CRT0603-BY-1212ELF]	12.3 Ohm [CR0402-FX-12R3GLF]
12 uH [SRR0908-120ML]	12 uH [SRR5028-120Y]	12.1 kOhm [CRT0805-BY-1212ELF]	12.4 kOhm [CR0402-FX-1242GLF]
12 uH [SRR1003-120M]	12 uH [SRR6028-120Y]	12.1 kOhm [CRT1206-BY-1212ELF]	12.4 kOhm [CR0603-FX-1242ELF]
12 uH [SRR1005-120M]	12 uH [SRR6038-120Y]	12.1 kOhm [CRT1206-FZ-1212ELF]	12.4 kOhm [CR0805-FX-1242ELF]
12 uH [SRR1205-120ML]	12 uH [SRR6040A-120M]	12.1 kOhm [CRT1206-FZ-1212ELF]	12.4 kOhm [CR1206-FX-1242ELF]
12 uH [SRR1206-120ML]	12 uH [SRR7045-120M]	12.1 Ohm [CR0402-FX-12R1GLF]	12.4 kOhm [CRT0805-BY-1242ELF]
12 uH [SRR1208-120ML]	12 uH [SRU1028-120Y]	12.1 Ohm [CR0603-FX-12R1ELF]	
12 uH [SRR1210-120M]	12 uH [SRU1048-120Y]		
12 uH [SRR1210A-120M]	12 uH [SRU8028-120Y]		

Multisim 14.1 Base Edition Components

12.4 kOhm [CRT0805-FX- 1242ELF]	12.7 kOhm [CRT0603-BY- 1272ELF]	120 kOhm [4306R- 101-124LF]	120 kOhm [4604X- 101-124LF]
12.4 Ohm [CR0402- FX-12R4GLF]	12.7 kOhm [CRT0805-BY- 1272ELF]	120 kOhm [4306R- 102-124]	120 kOhm [4605X- 101-124LF]
12.4 Ohm [CR0805- FX-12R4ELF]	12.7 Ohm [CR0402- FX-12R7GLF]	120 kOhm [4306R- 102-124LF]	120 kOhm [4606X- 101-124LF]
12.4 Ohm [CR1206- FX-12R4ELF]	12.7 Ohm [CR0603- FX-12R7ELF]	120 kOhm [4308M- 101-124]	120 kOhm [4606X- 102-124LF]
12.4 Ohm [CRM1206-FX- 12R4ELF]	12.7 Ohm [CR0805- FX-12R7ELF]	120 kOhm [4308M- 101-124LF]	120 kOhm [4606X- AP1-124LF]
12.7 kOhm [CR0402-FX- 1272GLF]	12.7 Ohm [CR1206- FX-12R7ELF]	120 kOhm [4308R- 101-124]	120 kOhm [4608H- 102-124LF]
12.7 kOhm [CR0603-FX- 1272ELF]	120 kOhm [4114R- 1-124]	120 kOhm [4308R- 101-124LF]	120 kOhm [4608X- 101-124LF]
12.7 kOhm [CR0805-FX- 1272ELF]	120 kOhm [4114R- 1-124LF]	120 kOhm [4308R- 102-124]	120 kOhm [4608X- 102-124LF]
12.7 kOhm [CR1206-FX- 1272ELF]	120 kOhm [4114R- 2-124]	120 kOhm [4308R- 102-124LF]	120 kOhm [4609X- 101-124LF]
12.7 kOhm [CR2512-FX- 1272ELF]	120 kOhm [4114R- 2-124LF]	120 kOhm [4310M- 101-124]	120 kOhm [4610X- 101-124LF]
12.7 kOhm [CRT0402-BZ- 1272GAS]	120 kOhm [4116R- 1-124]	120 kOhm [4310R- 101-124]	120 kOhm [4610X- 102-124LF]
12.7 kOhm [CRT0603-BX- 1272ELF]	120 kOhm [4116R- 1-124LF]	120 kOhm [4310R- 101-124LF]	120 kOhm [4610X- AP1-124LF]
	120 kOhm [4116R- 2-124]	120 kOhm [4310R- 102-124]	120 kOhm [4816P- 1-124]
	120 kOhm [4116R- 2-124LF]	120 kOhm [4310R- 102-124LF]	120 kOhm [4816P- 1-124LF]
	120 kOhm [4306R- 101-124]	120 kOhm [4416P- 2-124]	120 kOhm [4816P- 2-124]

Multisim 14.1 Base Edition Components

120 kOhm [4816P-2-124F]	120 kOhm [CR0603-FX-1203ELF]	120 kOhm [CRT1206-FX-1203ELF]	120 mOhm [PWR4525WR120J]
120 kOhm [4816P-2-124LF]	120 kOhm [CR0603-JW-124ELF]	120 mOhm [CRL0603-FW-R120ELF]	120 mOhm [PWR4525WR120JE]
120 kOhm [4816P-T01-124]	120 kOhm [CR0805-FX-1203ELF]	120 mOhm [CRL0603-JW-R120ELF]	120 nF [C0603C124K4RACTU]
120 kOhm [4816P-T01-124LF]	120 kOhm [CR0805-JW-124ELF]	120 mOhm [CRL0805-FW-R120ELF]	120 nF [C0603C124K8RACTU]
120 kOhm [4816P-T02-124]	120 kOhm [CR1206-FX-1203ELF]	120 mOhm [CRL0805-JW-R120ELF]	120 nF [C0805C124K1RACTU]
120 kOhm [4816P-T02-124LF]	120 kOhm [CR1206-JW-124ELF]	120 mOhm [CRL1206-FW-R120ELF]	120 nF [C0805C124K3RACTU]
120 kOhm [CAT16-124J4LF]	120 kOhm [CRM1206-FX-1203ELF]	120 mOhm [CRL1206-JW-R120ELF]	120 nF [C0805C124K4RACTU]
120 kOhm [CAT25-124JALF]	120 kOhm [CRM1206-JW-124ELF]	120 mOhm [CRL2010-FW-R120ELF]	120 nF [C0805C124K5RACTU]
120 kOhm [CAY10-124J2LF]	120 kOhm [CRM2010-JW-124ELF]	120 mOhm [CRL2010-JW-R120ELF]	120 nF [C1206C124K1RACTU]
120 kOhm [CAY16-1203F4LF]	120 kOhm [CRM2512-FX-1203ELF]	120 mOhm [CRM2512-FX-R120ELF]	120 nF [C1206C124K2RACTU]
120 kOhm [CAY16-124J4LF]			
120 kOhm [CAY16-124J8LF]			
120 kOhm [CR0402-FX-1203GLF]			
120 kOhm [CR0402-JW-124GLF]			

Multisim 14.1 Base Edition Components

120 nF [C1206C124K3RACT U]	120 nF [C1210F124K5RACT U]	120 nF [C1812F124K5RACT U]	120 nF [MDC10124K630A5 8P8TUBE]
120 nF [C1206C124K4RACT U]	120 nF [C1812C124K1GACT U]	120 nF [C2220C124K1GACT U]	120 nF [MDC15124K100B5 3P3TUBE]
120 nF [C1206C124K5RACT U]	120 nF [C1812C124K1HACT U]	120 nF [C2220C124K5GACT U]	120 nF [MDC15124K250B5 3P3TUBE]
120 nF [C1206C124M5UAC TU]	120 nF [C1812C124K2RACT U]	120 nF [C2225C124K1RACT U]	120 nF [MDC15124K400B5 3P3TUBE]
120 nF [C1210C124K1RACT U]	120 nF [C1812C124K5GACT U]	120 nF [GMC5.7124K50J33 TR12]	120 nF [MDC15124K50B53 P3TUBE]
120 nF [C1210C124K3HACT U]	120 nF [C1812C124K5HACT U]	120 nF [GMC7.3124K63K31 TR12]	120 nF [MDK15124K50B53 P3TUBE]
120 nF [C1210C124K5HACT U]	120 nF [C1812C124K5RACT U]	120 nF [MDC10124K100A5 2P3TUBE]	120 nF [MDS15124K50B53 P3TUBE]
120 nF [C1210C124K5RACT U]	120 nF [C1812C124M1UAC TU]	120 nF [MDC10124K250A5 2P3TUBE]	120 nF [MMC7.3124K50K3 1TR12]
120 nF [C1210F124K1RACT U]	120 nF [C1812F124K1RACT U]	120 nF [MDC10124K400A5 2P3TUBE]	120 Ohm [4108R-1- 121]
120 nF [C1210F124K3RACT U]	120 nF [C1812F124K2RACT U]	120 nF [MDC10124K50A52 P3TUBE]	120 Ohm [4108R-1- 121LF]
120 nF [C1210F124K4RACT U]	120 nF [C1812F124K3RACT U]	120 nF [MDC10124K630A5 8P7TUBE]	120 Ohm [4114R-1- 121]
			120 Ohm [4114R-1- 121LF]

Multisim 14.1 Base Edition Components

120 Ohm [4114R-2-121]	120 Ohm [4308H-102-121LF]	120 Ohm [4310R-101-121]	120 Ohm [4606H-102-121LF]
120 Ohm [4114R-2-121LF]	120 Ohm [4308M-102-121]	120 Ohm [4310R-101-121LF]	120 Ohm [4606X-101-121LF]
120 Ohm [4116R-1-121]	120 Ohm [4308M-102-121LF]	120 Ohm [4310R-102-121]	120 Ohm [4606X-102-121LF]
120 Ohm [4116R-1-121LF]	120 Ohm [4308R-101-121]	120 Ohm [4310R-102-121LF]	120 Ohm [4607X-101-121LF]
120 Ohm [4116R-2-121]	120 Ohm [4308R-101-121LF]	120 Ohm [4416P-1-121]	120 Ohm [4608M-101-121LF]
120 Ohm [4116R-2-121LF]	120 Ohm [4308R-102-121]	120 Ohm [4416P-2-121]	120 Ohm [4608X-101-121LF]
120 Ohm [4304M-102-121]	120 Ohm [4308R-102-121LF]	120 Ohm [4416P-T01-121]	120 Ohm [4608X-102-121LF]
120 Ohm [4304M-102-121LF]	120 Ohm [4309R-101-121]	120 Ohm [4416P-T02-121]	120 Ohm [4609X-101-121LF]
120 Ohm [4306M-102-121]	120 Ohm [4309R-101-121LF]	120 Ohm [4420P-1-121]	120 Ohm [4610X-101-121LF]
120 Ohm [4306M-102-121LF]	120 Ohm [4310H-101-121]	120 Ohm [4420P-2-121]	120 Ohm [4610X-102-121LF]
120 Ohm [4306R-101-121]	120 Ohm [4310H-101-121LF]	120 Ohm [4420P-T01-121]	120 Ohm [4610X-AP1-121LF]
120 Ohm [4306R-101-121LF]	120 Ohm [4310H-102-121]	120 Ohm [4604X-101-121LF]	120 Ohm [4612X-101-121LF]
120 Ohm [4306R-102-121]	120 Ohm [4310H-102-121LF]	120 Ohm [4604X-102-121LF]	120 Ohm [4612X-102-121LF]
120 Ohm [4306R-102-121LF]	120 Ohm [4310M-102-121]	120 Ohm [4605M-101-121LF]	120 Ohm [4614X-102-121LF]
120 Ohm [4308H-102-121]	120 Ohm [4310M-102-121LF]	120 Ohm [4605X-101-121LF]	120 Ohm [4814P-1-121LF]

Multisim 14.1 Base Edition Components

120 Ohm [4814P-2-121]	120 Ohm [4820P-T01-121]	120 Ohm [CR0603-FX-1200GLF]	120 Ohm [CRM2512-JW-121ELF]
120 Ohm [4814P-T01-121]	120 Ohm [CAT10-121J4LF]	120 Ohm [CR0603-JW-121ELF]	120 Ohm [CRT0603-BY-1200ELF]
120 Ohm [4814P-T01-121LF]	120 Ohm [CAT16-1200F4LF]	120 Ohm [CR0603-JW-121GLF]	120 Ohm [CRT0805-DZ-1200ELF]
120 Ohm [4816P-1-121]	120 Ohm [CAT16-121J2LF]	120 Ohm [CR0805-FX-1200ELF]	120 Ohm [PWR163S-25-1200F]
120 Ohm [4816P-1-121LF]	120 Ohm [CAT16-121J4LF]	120 Ohm [CR0805-FX-1200GLF]	120 Ohm [PWR163S-25-1200F]
120 Ohm [4816P-2-121]	120 Ohm [CAT16-121J8LF]	120 Ohm [CR0805-JW-121ELF]	120 Ohm [PWR163S-25-1200JE]
120 Ohm [4816P-2-121LF]	120 Ohm [CAT25-121JALF]	120 Ohm [CR1206-FX-1200ELF]	120 Ohm [PWR220T-20-1200F]
120 Ohm [4816P-4-121]	120 Ohm [CAY10-121J4LF]	120 Ohm [CR1206-FX-1200GLF]	120 Ohm [PWR221T-30-1200F]
120 Ohm [4816P-T01-121]	120 Ohm [CAY16-1200F4LF]	120 Ohm [CR1206-JW-121ELF]	120 Ohm [PWR2615W1200FE]
120 Ohm [4816P-T01-121LF]	120 Ohm [CAY16-121J4LF]	120 Ohm [CR2010-JW-121ELF]	120 Ohm [PWR263S-35-1200F]
120 Ohm [4816P-T02-121]	120 Ohm [CAY16-121J8LF]	120 Ohm [CR2512-JW-121ELF]	120 Ohm [PWR263S-35-1200J]
120 Ohm [4816P-T02-121LF]	120 Ohm [CAY17-121JALF]	120 Ohm [CRM1206-FX-1200ELF]	120 Ohm [PWR4525W1200F]
120 Ohm [4818P-2-121]	120 Ohm [CR0402-FX-1200GLF]	120 Ohm [CRM2010-FX-1200ELF]	
120 Ohm [4818P-T02-121LF]	120 Ohm [CR0402-JW-121GLF]	120 Ohm [CRM2512-FX-1200ELF]	
120 Ohm [4820P-1-121]	120 Ohm [CR0603-FX-1200ELF]		

Multisim 14.1 Base Edition Components

120 Ohm [PWR4525W1200FE]	120 pF [C1206C121K1GACT U]	120 uF [10SVPC120M]	120 uF [A700X127M010AT E010]
120 pF [03029BR121AKZC]	120 pF [C1206C121K2GACT U]	120 uF [10SVPC120MV]	120 uF [A700X127M010AT E015]
120 pF [C0402C121K1HACT U]	120 pF [C1206C121K5GACT U]	120 uF [16SVPC120M]	120 uF [EEFCS0G121R]
120 pF [C0402C121K3HACT U]	120 pF [C1206C121KBGAC TU]	120 uF [20SEPF120M]	120 uF [EEFCX0J121R]
120 pF [C0402C121K5GACT U]	120 pF [C1206C121KDGAC TU]	120 uF [35SVPF120M]	120 uF [EEFLR0G121R]
120 pF [C0402C121K5HACT U]	120 pF [C1206C121KDGAC TU]	120 uF [6SVPC120MV]	120 uF [EEFSR0G121R]
120 pF [C0402C121K5HACT U]	120 pF [C1210C121KBGAC TU]	120 uF [6TPE120MAZB]	120 uF [EEFSX0J121E7]
120 pF [C0603C121K1GACT U]	120 pF [C1210C121KBGAC TU]	120 uF [A700D127M004AT E015]	120 uF [A700D127M004AT E018]
120 pF [C0603C121K5GACT U]	120 pF [C1812C121KBGAC TU]	120 uF [A700D127M004AT E018]	120 uH [SDE0604A- 121K]
120 pF [C0603C121K5GACT U]	120 pF [C1825C121KBGAC TU]	120 uF [A700D127M006AT E012]	120 uH [SDE0805A- 121K]
120 pF [C0805C121K1GACT U]	120 pF [C1825C121KBGAC TU]	120 uF [A700D127M006AT E015]	120 uH [SDE1006A- 121K]
120 pF [C0805C121K2GACT U]	120 pF [C2220C121KBGAC TU]	120 uF [A700D127M006AT E015]	120 uH [SDR0302- 121KL]
120 pF [C0805C121K2GACT U]	120 pF [C2225C121KBGAC TU]	120 uF [A700D127M006AT E018]	120 uH [SDR0403- 121KL]
120 pF [C0805C121K5GACT U]	120 pF [CA064C121K5GAC TU]	120 uF [A700V127M002AT E018]	120 uH [SDR0503- 121KL]

Multisim 14.1 Base Edition Components

120 uH [SDR0603-121KL]	120 uH [SRR1003-121M]	120 uH [SRU1028-121Y]	121 Ohm [CR2512-FX-1210ELF]
120 uH [SDR0604-121KL]	120 uH [SRR1005-121K]	120 uH [SRU1028A-121Y]	121 Ohm [CRM1206-FX-1210ELF]
120 uH [SDR0703-121KL]	120 uH [SRR1205-121KL]	120V_100W	121 Ohm [CRT0402-FZ-1210GLF]
120 uH [SDR0805-121KL]	120 uH [SRR1206-121YL]	120V_250W	121 Ohm [CRT0805-BY-1210ELF]
120 uH [SDR0906-121KL]	120 uH [SRR1208-121YL]	121 kOhm [CR0402-FX-1213GLF]	121 Ohm [CRT1206-BY-1210ELF]
120 uH [SDR1006-121KL]	120 uH [SRR1210-121M]	121 kOhm [CR0603-FX-1213ELF]	124 kOhm [CHV2512-FX-1243ELF]
120 uH [SDR1307-121KL]	120 uH [SRR1210A-121M]	121 kOhm [CR0805-FX-1213ELF]	124 kOhm [CR0402-FX-1243GLF]
120 uH [SDR1307A-121K]	120 uH [SRR1240-121K]	121 kOhm [CR1206-FX-1213ELF]	124 kOhm [CR0603-FX-1243ELF]
120 uH [SRR0735A-121M]	120 uH [SRR1260-121K]	121 kOhm [CRT1206-FZ-1213ELF]	124 Ohm [CAY16-1210F4LF]
120 uH [SRR0745A-121M]	120 uH [SRR1260A-121K]	121 Ohm [CR0402-FX-1210GLF]	121 Ohm [CR0603-FX-1210ELF]
120 uH [SRR0804-121K]	120 uH [SRR1280-121K]	121 Ohm [CR0805-FX-1210ELF]	124 Ohm [CR0402-FX-1240GLF]
120 uH [SRR0805-121K]	120 uH [SRR4018-121Y]	121 Ohm [CR1206-FX-1210ELF]	124 Ohm [CR0603-FX-1240ELF]
120 uH [SRR0905-121K]	120 uH [SRR4028-121Y]		
120 uH [SRR0906-121YL]	120 uH [SRR5018-121Y]		
120 uH [SRR0908-121YL]	120 uH [SRR7045-121M]		

Multisim 14.1 Base Edition Components

124 Ohm [CR0805-FX-1240ELF]	127 Ohm [CR0805-FX-1270ELF]	13 kOhm [CR0603-JW-133ELF]	13 kOhm [CRT0805-BY-1302ELF]
124 Ohm [CR1206-FX-1240ELF]	127 Ohm [CR1206-FX-1270ELF]	13 kOhm [CR0603-JW-133GLF]	13 Ohm [CAT10-130J4LF]
124 Ohm [CRT0805-BY-1240ELF]	1-282834-0 1294	13 kOhm [CR0805-FX-1302ELF]	13 Ohm [CAT16-130J4GLF]
124 Ohm [CRT1206-BY-1240ELF]	12A02CH-TL-E 12A02MH-TL-E	13 kOhm [CR0805-FX-1302GLF]	13 Ohm [CAT16-130J4LF]
125 mOhm [PWR4525WR125F E]	12V_10W 12V_25W	13 kOhm [CR0805-JW-133ELF]	13 Ohm [CAT25-130JALF]
127 kOhm [CR0603-FX-1273ELF]	13 kOhm [4116R-1-133] 13 kOhm [CAT10-133J4LF]	13 kOhm [CR0805-JW-133GLF]	13 Ohm [CAY10-130J2LF]
127 kOhm [CR0805-FX-1273ELF]	13 kOhm [CAT16-1302F4LF]	13 kOhm [CR1206-FX-1302ELF]	13 Ohm [CAY16-130J4LF]
127 kOhm [CR1206-FX-1273ELF]	13 kOhm [CAT16-133J4LF]	13 kOhm [CR1206-JW-133ELF]	13 Ohm [CR0402-FX-13R0GLF]
127 kOhm [CRT0603-AZ-1273ELF]	13 kOhm [CAY10-133J4LF]	13 kOhm [CRM2512-FX-1302ELF]	13 Ohm [CR0603-FX-13R0ELF]
127 kOhm [CRT1206-BY-1273ELF]	13 kOhm [CAY16-1302F4LF]	13 kOhm [CRM2512-JW-133ELF]	13 Ohm [CR0603-JW-130ELF]
127 Ohm [CR0402-FX-1270GLF]	13 kOhm [CAY16-133J4LF]	13 kOhm [CRT0603-BY-1302ELF]	13 Ohm [CR0805-FX-13R0ELF]
127 Ohm [CR0603-FX-1270ELF]	13 kOhm [CR0402-FX-1302GLF]	13 kOhm [CRT0603-FY-1302ELF]	13 Ohm [CR0805-FX-13R0GLF]
	13 kOhm [CR0402-JW-133GLF]	13 kOhm [CRT0603-FY-1302ELF]	13 Ohm [CR0805-JW-130ELF]
	13 kOhm [CR0603-FX-1302ELF]	13 kOhm [CRT0805-BW-1302ELF]	13 Ohm [CR1206-FX-13R0ELF]
			13 Ohm [CR1206-JW-130ELF]

Multisim 14.1 Base Edition Components

13 Ohm [CRM2512-JW-130ELF]	13.3 kOhm [CR0402-FX-1332GLF]	13.7 kOhm [CR0805-FX-1372ELF]	130 kOhm [CR1206-FX-1303ELF]
13 pF [C0603C130K2GACTU]	13.3 kOhm [CR0603-FX-1332ELF]	13.7 kOhm [CR1206-FX-1372ELF]	130 kOhm [CR1206-JW-134ELF]
13 pF [C0603C130K5GACTU]	13.3 kOhm [CR0805-FX-1332ELF]	13.7 kOhm [CRT0805-BY-1372ELF]	130 kOhm [CR2010-JW-134ELF]
13 pF [C0805C130K5GACTU]	13.3 kOhm [CR1206-FX-1332ELF]	13.7 Ohm [CR0603-FX-13R7ELF]	130 kOhm [CRM2010-FX-1303ELF]
13 pF [C0805C130KBGAC TU]	13.3 kOhm [CRT0805-BY-1332ELF]	13.7 Ohm [CRT0805-BY-13R7ELF]	130 kOhm [CRT0402-BY-1303GLF]
13 pF [C1206C130KBGAC TU]	13.3 Ohm [CR0603-FX-13R3ELF]	130 kOhm [CAY16-134J4LF]	130 kOhm [CRT0603-BY-1303ELF]
13 pF [C1210C130KBGAC TU]	13.3 Ohm [CR0805-FX-13R3ELF]	130 kOhm [CR0402-FX-1303GLF]	130 kOhm [CRT1206-BY-1303ELF]
13 pF [C1812C130KBGAC TU]	13.3 Ohm [CR1206-FX-13R3ELF]	130 kOhm [CR0402-JW-134GLF]	130 kOhm [PWR220T-20-1303F]
13 pF [C1825C130KBGAC TU]	13.3 Ohm [CR2512-FX-13R3ELF]	130 kOhm [CR0603-FX-1303ELF]	130 kOhm [PWR220T-20-1303J]
13 pF [C2220C130KBGAC TU]	13.3 Ohm [CRT1206-BY-13R3ELF]	130 kOhm [CR0603-JW-134ELF]	130 kOhm [PWR263S-20-1303F]
13 pF [C2225C130KBGAC TU]	13.7 kOhm [CR0402-FX-1372GLF]	130 kOhm [CR0805-FX-1303ELF]	130 kOhm [PWR263S-20-1303J]
	13.7 kOhm [CR0603-FX-1372ELF]	130 kOhm [CR0805-JW-134ELF]	

Multisim 14.1 Base Edition Components

130 kOhm [PWR263S-35-1303F]	130 mOhm [CRL2512-JW-R130ELF]	130 Ohm [CAT25-131JALF]	130 Ohm [CRT0805-BY-1300ELF]
130 kOhm [PWR263S-35-1303J]	130 mOhm [CRM1206-JX-R130ELF]	130 Ohm [CAY16-131J4LF]	130 Ohm [PWR263S-20-1300J]
130 mOhm [CRL0603-FW-R130ELF]	130 Ohm [4116R-1-131]	130 Ohm [CR0201-JW-131GLF]	130 Ohm [PWR263S-35-1300J]
130 mOhm [CRL0603-JW-R130ELF]	130 Ohm [4116R-1-131LF]	130 Ohm [CR0402-JW-131GLF]	130 Ohm [PWR5322W1300JE]
130 mOhm [CRL0805-FW-R130ELF]	130 Ohm [4308M-102-131]	130 Ohm [CR0603-FX-1300ELF]	130 pF [C0402C131K1HACTU]
130 mOhm [CRL0805-JW-R130ELF]	130 Ohm [4308M-102-131LF]	130 Ohm [CR0603-FX-1300HLF]	130 pF [C0402C131K3HACTU]
130 mOhm [CRL1206-FW-R130ELF]	130 Ohm [4310R-102-131]	130 Ohm [CR0603-JW-131ELF]	130 pF [C0402C131K5HACTU]
130 mOhm [CRL1206-JW-R130ELF]	130 Ohm [4608X-102-131LF]	130 Ohm [CR0805-FX-1300ELF]	130 pF [C0805H131K3GAC TU]
130 mOhm [CRL2010-FW-R130ELF]	130 Ohm [4609X-101-131LF]	130 Ohm [CR1206-FX-1300ELF]	130 pF [C1206C131KBGAC TU]
130 mOhm [CRL2010-JW-R130ELF]	130 Ohm [4816P-2-131]	130 Ohm [CR1206-JW-131ELF]	130 pF [C1210C131KBGAC TU]
130 mOhm [CRL2512-FW-R130ELF]	130 Ohm [4816P-2-131LF]	130 Ohm [CRM2512-FX-1300ELF]	130 pF [C1812C131KBGAC TU]
	130 Ohm [4816P-T02-131]	130 Ohm [CRT0402-DY-1300GLF]	

Multisim 14.1 Base Edition Components

130 pF [C1825C131KBGAC TU]	133 Ohm [CR1206- FX-1330ELF]	137 Ohm [CR1206- FX-1370ELF]	14.3 kOhm [CR1206-FX- 1432ELF]
130 pF [C2220C131KBGAC TU]	133 Ohm [CR2010- FX-1330ELF]	14 kOhm [CR0402- FX-1402GLF]	14.3 Ohm [CR0402- FX-14R3GLF]
130 pF [C2225C131KBGAC TU]	133 Ohm [CRT0402-FZ- 1330GLF]	14 kOhm [CR0603- FX-1402ELF]	14.3 Ohm [CR0603- FX-14R3ELF]
133 kOhm [CR0402-FX- 1333GLF]	135 Ohm [PWR4525W1350F]	14 kOhm [CR0805- FX-1402ELF]	14.3 Ohm [CR0805- FX-14R3ELF]
133 kOhm [CR0603-FX- 1333ELF]	135 Ohm [PWR4525W1350FE]	14 kOhm [CR1206- FX-1402ELF]	14.3 Ohm [CR1206- FX-14R3ELF]
133 kOhm [CR0805-FX- 1333ELF]	137 kOhm [CAT16- 1373F4LF]	14 kOhm [CRT0402-CY- 1402GLF]	14.7 kOhm [CR0402-FX- 1472GLF]
133 kOhm [CR1206-FX- 1333ELF]	137 kOhm [CR0402-FX- 1373GLF]	14 Ohm [CAY16- 14R0F4LF]	14.7 kOhm [CR0603-FX- 1472ELF]
133 kOhm [CR1206-FX- 1333ELF]	137 kOhm [CR0603-FX- 1373ELF]	14 Ohm [CR0402- FX-14R0GLF]	14.7 kOhm [CR0805-FX- 1472ELF]
133 kOhm [CRT0603-AZ- 1333ELF]	137 kOhm [CR0805-FX- 1373ELF]	14 Ohm [CR0805- FX-14R0ELF]	14.7 kOhm [CR1206-FX- 1472ELF]
133 kOhm [CRT0805-BY- 1333ELF]	137 kOhm [CR1206-FX- 1373ELF]	14.3 kOhm [CR0402-FX- 1432GLF]	14.7 kOhm [CRT0402-BX- 1472GLF]
133 Ohm [CR0402- FX-1330GLF]	137 Ohm [CR0402- FX-1370GLF]	14.3 kOhm [CR0603-FX- 1432ELF]	14.7 kOhm [CRT0805-BY- 1472ELF]
133 Ohm [CR0603- FX-1330ELF]	137 Ohm [CR0603- FX-1370ELF]	14.3 kOhm [CR0805-FX- 1432ELF]	14.7 Ohm [CR0402- FX-14R7GLF]
133 Ohm [CR0805- FX-1330ELF]	137 Ohm [CR0805- FX-1370ELF]		14.7 Ohm [CR0603- FX-14R7ELF]

Multisim 14.1 Base Edition Components

14.7 Ohm [CR0805-FX-14R7ELF]	143 kOhm [CR0402-FX-1433GLF]	147 kOhm [CR1206-FX-1473ELF]	15 kOhm [4116R-2-153LF]
14.7 Ohm [CR1206-FX-14R7ELF]	143 kOhm [CR0603-FX-1433ELF]	147 kOhm [CRT0402-BY-1473GLF]	15 kOhm [4306H-101-153]
14.7 Ohm [CRT0402-FZ-14R7GLF]	143 kOhm [CR0805-FX-1433ELF]	147 Ohm [CR0603-FX-1470ELF]	15 kOhm [4306H-101-153LF]
140 kOhm [CR0402-FX-1403GLF]	143 kOhm [CR1206-FX-1433ELF]	147 Ohm [CR0805-FX-1470ELF]	15 kOhm [4306M-101-153]
140 kOhm [CR0603-FX-1403ELF]	143 kOhm [CRT0603-AZ-1433ELF]	147 Ohm [CR1206-FX-1470ELF]	15 kOhm [4306M-102-153]
140 kOhm [CR0805-FX-1403ELF]	143 Ohm [CR0402-FX-1430GLF]	147 Ohm [CRT0402-FZ-1470GLF]	15 kOhm [4306M-102-153LF]
140 kOhm [CR1206-FX-1403ELF]	143 Ohm [CR0603-FX-1430ELF]	15 kOhm [4108R-1-153LF]	15 kOhm [4306R-101-153]
140 Ohm [CAT16-1400F4LF]	143 Ohm [CR0805-FX-1430ELF]	15 kOhm [4114R-1-153]	15 kOhm [4306R-101-153LF]
140 Ohm [CAT25-141JALF]	143 Ohm [CR1206-FX-1430ELF]	15 kOhm [4114R-1-153LF]	15 kOhm [4306R-102-153]
140 Ohm [CR0402-FX-1400GLF]	147 kOhm [CR0402-FX-1473GLF]	15 kOhm [4114R-2-153]	15 kOhm [4306R-102-153LF]
140 Ohm [CR0603-FX-1400ELF]	147 kOhm [CR0603-FX-1473ELF]	15 kOhm [4114R-2-153LF]	15 kOhm [4308H-101-153]
140 Ohm [CR0805-FX-1400ELF]	147 kOhm [CR0805-FX-1473ELF]	15 kOhm [4116R-1-153]	15 kOhm [4308H-102-153]
140 Ohm [CR1206-FX-1400ELF]	147 kOhm [CR0805-FX-1473ELF]	15 kOhm [4116R-1-153LF]	15 kOhm [4308H-102-153LF]
		15 kOhm [4116R-2-153]	15 kOhm [4308R-101-153]

Multisim 14.1 Base Edition Components

15 kOhm [4308R-101-153LF]	15 kOhm [4416P-1-153]	15 kOhm [4608X-102-153LF]	15 kOhm [4814P-T02-153LF]
15 kOhm [4308R-102-153]	15 kOhm [4416P-T01-153]	15 kOhm [4608X-AP1-153LF]	15 kOhm [4816P-1-153]
15 kOhm [4308R-102-153LF]	15 kOhm [4420P-2-153]	15 kOhm [4608X-AP2-153LF]	15 kOhm [4816P-1-153LF]
15 kOhm [4309R-101-153]	15 kOhm [4420P-T02-153]	15 kOhm [4609H-101-153LF]	15 kOhm [4816P-2-153]
15 kOhm [4309R-101-153LF]	15 kOhm [4604X-101-153LF]	15 kOhm [4609X-101-153LF]	15 kOhm [4816P-2-153LF]
15 kOhm [4310H-101-153]	15 kOhm [4604X-102-153LF]	15 kOhm [4610X-101-153LF]	15 kOhm [4816P-T01-153]
15 kOhm [4310H-101-153LF]	15 kOhm [4605H-101-153LF]	15 kOhm [4610X-102-153LF]	15 kOhm [4816P-T01-153LF]
15 kOhm [4310M-101-153]	15 kOhm [4605X-101-153LF]	15 kOhm [4610X-AP1-153LF]	15 kOhm [4816P-T02-153]
15 kOhm [4310M-101-153LF]	15 kOhm [4606X-101-153LF]	15 kOhm [4814P-1-153]	15 kOhm [4816P-T02-153LF]
15 kOhm [4310M-102-153]	15 kOhm [4606X-102-153LF]	15 kOhm [4814P-1-153LF]	15 kOhm [4818P-2-153]
15 kOhm [4310M-102-153LF]	15 kOhm [4606X-AP2-153LF]	15 kOhm [4814P-2-153]	15 kOhm [4818P-T02-153]
15 kOhm [4310R-101-153]	15 kOhm [4607M-101-153LF]	15 kOhm [4814P-2-153LF]	15 kOhm [4820P-2-153]
15 kOhm [4310R-101-153LF]	15 kOhm [4607X-101-153LF]	15 kOhm [4814P-T01-153]	15 kOhm [4820P-T01-153]
15 kOhm [4310R-102-153]	15 kOhm [4608H-102-153LF]	15 kOhm [4814P-T01-153LF]	15 kOhm [4820P-T02-153]
15 kOhm [4310R-102-153LF]	15 kOhm [4608X-101-153LF]	15 kOhm [4814P-T02-153]	15 kOhm [CAT10-153J4LF]

Multisim 14.1 Base Edition Components

15 kOhm [CAT16-1502F4LF]	15 kOhm [CR0603-FX-1502ELF]	15 kOhm [CRT0402-BY-1502GLF]	15 kOhm [PWR4525W1502J]
15 kOhm [CAT16-1502F8LF]	15 kOhm [CR0603-JW-153ELF]	15 kOhm [CRT0603-BY-1502ELF]	15 kOhm [PWR4525W1502JE]
15 kOhm [CAT16-153J4LF]	15 kOhm [CR0603-JW-153GLF]	15 kOhm [CRT0603-PW-1502ELF]	15 kOhm [PWR5322W1502JE]
15 kOhm [CAT16-153J8LF]	15 kOhm [CR0805-FX-1502ELF]	15 kOhm [CRT0805-BY-1502ELF]	15 kOhm [PWR6327W1502J]
15 kOhm [CAT25-153JALF]	15 kOhm [CR0805-JW-153GLF]	15 kOhm [CRT0805-DY-1502ELF]	15 mH [SDR0503-153JL]
15 kOhm [CAY10-153J2LF]	15 kOhm [CR1206-FX-1502ELF]	15 kOhm [PWR220T-20-1502J]	15 mH [SRR0908-153YL]
15 kOhm [CAY10-153J4LF]	15 kOhm [CR1206-JW-153ELF]	15 kOhm [PWR220T-35-1502J]	15 mOhm [CRA2512-FZ-R015ELF]
15 kOhm [CAY16-153J4LF]	15 kOhm [CRM1206-FX-1502ELF]	15 kOhm [PWR221T-30-1502F]	15 mOhm [CRF2512-FZ-R015ELF]
15 kOhm [CAY16-153J8LF]	15 kOhm [CRM1206-JW-153ELF]	15 kOhm [PWR263S-20-1502F]	15 mOhm [PWR1913WR015F]
15 kOhm [CAY17-153JALF]	15 kOhm [CRM2512-FX-1502ELF]	15 kOhm [PWR263S-20-1502J]	15 mOhm [PWR1913WR015FE]
15 kOhm [CR0201-FW-1502GLF]	15 kOhm [CRM2512-JW-153ELF]	15 kOhm [PWR4525W1502FE]	15 mOhm [PWR1913WR015JE]
15 kOhm [CR0201-JW-153GLF]			
15 kOhm [CR0402-FX-1502GLF]			
15 kOhm [CR0402-JW-153GLF]			

Multisim 14.1 Base Edition Components

15 mOhm [PWR2615WR015F]	15 nF [03063C153KAT2A]	15 nF [C0603C153K4RACT U]	15 nF [C0805C153K8RACT U]
15 mOhm [PWR2615WR015F E]	15 nF [0306YC153KAT2A]	15 nF [C0603C153K5RACT U]	15 nF [C0805C153KARACT U]
15 mOhm [PWR2615WR015J]	15 nF [0306ZC153KAT2A]	15 nF [C0805C153K1GACT U]	15 nF [C0805C153M5UAC TU]
15 mOhm [PWR2615WR015JE]	15 nF [06125C153KAT2W]	15 nF [C0805C153K1HACT U]	15 nF [C0805F153K1RACT U]
15 mOhm [PWR4412- 2SBR0150F]	15 nF [C0402C153K4RACT U]	15 nF [C0805C153K1RACT U]	15 nF [C0805F153K3RACT U]
15 mOhm [PWR4412- 2SCR0150F]	15 nF [C0402C153K5RACT U]	15 nF [C0805C153K3HACT U]	15 nF [C0805F153K4RACT U]
15 mOhm [PWR4412- 2SDR0150F]	15 nF [C0402C153K8PACT U]	15 nF [C0805C153K3RACT U]	15 nF [C0805F153K5RACT U]
15 mOhm [PWR4412- 2SDR0150J]	15 nF [C0402C153K8RACT U]	15 nF [C0805C153K4RACT U]	15 nF [C1206C153K1HACT U]
15 mOhm [PWR4525WR015J]	15 nF [C0402C153K9PACT U]	15 nF [C0805C153K5GACT U]	15 nF [C1206C153K1RACT U]
15 mOhm [PWR4525WR015JE]	15 nF [C0402C153K9RACT U]	15 nF [C0805C153K5HACT U]	15 nF [C1206C153K2RACT U]
15 mOhm [PWR6327WR015J]	15 nF [C0603C153K1RACT U]	15 nF [C0805C153K5RACT U]	15 nF [C1206C153K3HACT U]
15 mOhm [PWR6327WR015JE]	15 nF [C0603C153K3RACT U]		

Multisim 14.1 Base Edition Components

15 nF [C1206C153K4RACT U]	15 nF [C1210C153K5RACT U]	15 nF [C2225C153K5GACT U]	15 nF [MMC5.7153K250J 33TR12]
15 nF [C1206C153K5HACT U]	15 nF [C1210C153KARACT U]	15 nF [CA064C153K5RACT U]	15 nF [MMC5.7153K50J3 1TR12]
15 nF [C1206C153K5RACT U]	15 nF [C1812C153K1GACT U]	15 nF [GMC5.7152K250J3 1TR12]	15 nF [MMC7.3153K250K 31TR12]
15 nF [C1206C153KARACT U]	15 nF [C1812C153K1HACT U]	15 nF [GMC5.7153K100J3 1TR12]	15 nF [MMC7.3153K400K 37TR12]
15 nF [C1206C153M5UAC TU]	15 nF [C1812C153K1RACT U]	15 nF [GMC5.7153K50J31 TR12]	15 nF [MMC7.3153K50K3 1TR12]
15 nF [C1210C153K1GACT U]	15 nF [C1812C153K2RACT U]	15 nF [GMC7.3152K250K3 1TR12]	15 nF [SPC10.2153K100A 31TR16]
15 nF [C1210C153K1HACT U]	15 nF [C1812C153K5GACT U]	15 nF [GMC7.3152K63K31 TR12]	15 nF [SPC10.2153K250A 31TR16]
15 nF [C1210C153K1RACT U]	15 nF [C1812C153K5HACT U]	15 nF [GMC7.3153K250K3 1TR12]	15 nF [SPC10.2153K400A 31TR16]
15 nF [C1210C153K2RACT U]	15 nF [C1812C153K5RACT U]	15 nF [GMC7.3153K63K31 TR12]	15 nF [SPC10.2153K630A 31TR16]
15 nF [C1210C153K3HACT U]	15 nF [C1825C153K5GACT U]	15 nF [GPC7.3153K63K31 TR12]	15 nF [SPC7.3153K100K33 TR12]
15 nF [C1210C153K5HACT U]	15 nF [C2220C153K2GACT U]	15 nF [LD17YC153KAB2S]	15 nF [SPC7.3153K250K37 TR12]

Multisim 14.1 Base Edition Components

15 Ohm [4114R-1-150LF]	15 Ohm [4816P-T01-150LF]	15 Ohm [CR0402-JW-150GLF]	15 Ohm [CRM2512-FX-15R0ELF]
15 Ohm [4116R-1-150]	15 Ohm [4820P-T01-150]	15 Ohm [CR0603-FX-15R0ELF]	15 Ohm [CRM2512-JW-150ELF]
15 Ohm [4116R-1-150LF]	15 Ohm [CAT10-150J4LF]	15 Ohm [CR0603-JW-150ELF]	15 Ohm [CRT0402-DZ-15R0GLF]
15 Ohm [4116R-2-150]	15 Ohm [CAT16-150J2LF]	15 Ohm [CR0603-JW-150GLF]	15 Ohm [CRT0603-BZ-15R0EAS]
15 Ohm [4116R-2-150LF]	15 Ohm [CAT16-150J4LF]	15 Ohm [CR0805-FX-15R0ELF]	15 Ohm [CRT0805-BY-15R0ELF]
15 Ohm [4308H-102-150]	15 Ohm [CAT16-15R0F4LF]	15 Ohm [CR0805-JW-150ELF]	15 Ohm [CRT0805-DY-15R0ELF]
15 Ohm [4308H-102-150LF]	15 Ohm [CAT25-150JALF]	15 Ohm [CR0805-JW-150GLF]	15 Ohm [CRT1206-BY-15R0ELF]
15 Ohm [4416P-T01-150]	15 Ohm [CAY10-150J2LF]	15 Ohm [CR1206-FX-15R0ELF]	15 Ohm [FW10A15R0JA]
15 Ohm [4606X-102-150LF]	15 Ohm [CAY10-150J4LF]	15 Ohm [CR1206-JW-150ELF]	15 Ohm [FW20A15R0JA]
15 Ohm [4608X-102-150LF]	15 Ohm [CAY16-150J4LF]	15 Ohm [CR2010-FX-15R0ELF]	15 Ohm [FW30A15R0JA]
15 Ohm [4609X-101-150LF]	15 Ohm [CAY16-150J8LF]	15 Ohm [CR2010-JW-150ELF]	15 Ohm [FW50A15R0JA]
15 Ohm [4610X-101-150LF]	15 Ohm [CAY16-15R0F4LF]	15 Ohm [CR2512-FX-15R0ELF]	15 Ohm [FW70A15R0JA]
15 Ohm [4816P-1-150]	15 Ohm [CR0201-FW-15R0GLF]	15 Ohm [CRM1206-FX-15R0ELF]	15 Ohm [PWR163S-25-15R0F]
15 Ohm [4816P-1-150LF]	15 Ohm [CR0201-JW-150GLF]	15 Ohm [CRM2010-FX-15R0ELF]	15 Ohm [PWR163S-25-15R0FE]
15 Ohm [4816P-T01-150]	15 Ohm [CR0402-FX-15R0GLF]		

Multisim 14.1 Base Edition Components

15 Ohm [PWR163S-25-15R0J]	15 Ohm [PWR2615W15R0JE]	15 pF [C0201C150K3GACT U]	15 pF [C0805C150K3GACT U]
15 Ohm [PWR163S-25-15R0JE]	15 Ohm [PWR263S-20-15R0F]	15 pF [C0402C150K3GACT U]	15 pF [C0805C150K4GACT U]
15 Ohm [PWR2010W15R0JE]	15 Ohm [PWR263S-20-15R0FE]	15 pF [C0402C150K4GACT U]	15 pF [C0805C150K5GACT U]
15 Ohm [PWR220T-20-15R0F]	15 Ohm [PWR263S-20-15R0J]	15 pF [C0402C150K5GACT U]	15 pF [C0805C150KBGAC TU]
15 Ohm [PWR220T-20-15R0J]	15 Ohm [PWR263S-35-15R0F]	15 pF [C0402C150K8GACT U]	15 pF [C1206C150K1GACT U]
15 Ohm [PWR220T-35-15R0F]	15 Ohm [PWR263S-35-15R0FE]	15 pF [C0603C150K1GACT U]	15 pF [C1206C150K2GACT U]
15 Ohm [PWR220T-35-15R0J]	15 Ohm [PWR263S-35-15R0J]	15 pF [C0603C150K2GACT U]	15 pF [C1206C150K5GACT U]
15 Ohm [PWR221T-30-15R0F]	15 Ohm [PWR4318W15R0JE]	15 pF [C0603C150K4GACT U]	15 pF [C1206C150KBGAC TU]
15 Ohm [PWR221T-30-15R0J]	15 Ohm [PWR4525W15R0J]	15 pF [C0603C150K5GACT U]	15 pF [C1206C150KGGAC TU]
15 Ohm [PWR221T-50-15R0J]	15 Ohm [PWR4525W15R0JE]	15 pF [C0805C150K1GACT U]	15 pF [C1210C150KBGAC TU]
15 Ohm [PWR2615W15R0J]	15 Ohm [PWR6327W15R0J]	15 pF [C0805C150K2GACT U]	15 pF [C1812C150KBGAC TU]
	15 Ohm [PWR6327W15R0JE]		

Multisim 14.1 Base Edition Components

15 pF [C1825C150KBGAC TU]	15 uF [C1210C156K9PACT U]	15 uF [T409E156M004AH 4250]	15 uF [T491B156M006AT]
15 pF [C2220C150KBGAC TU]	15 uF [EEFCS1C150R]	15 uF [T409H156M025AH 4250]	15 uF [T491B156M010AT]
15 pF [C2225C150KBGAC TU]	15 uF [EEFCS1D150R]	15 uF [T419B156M004AH 4250]	15 uF [T491B156M016AT]
15 pF [CA064C150K4GAC TU]	15 uF [EEFCS1E150R]	15 uF [T419D156M010AH 4250]	15 uF [T491C156M006AT]
15 pF [CA064C150K5GAC TU]	15 uF [EEFCX1C150R]	15 uF [T429B156M004AH 4250]	15 uF [T491C156M010AT]
15 uF [12TPC15M]	15 uF [EEFCX1E150R]	15 uF [T429F156M010AH 4250]	15 uF [T491C156M016AT]
15 uF [16TQC15M]	15 uF [EEFCX1V150R]	15 uF [T429F156M010AH 4250]	15 uF [T491C156M025AT]
15 uF [25TQC15MV]	15 uF [EEFHX1C150R]	15 uF [T429F156M020AH 4250]	15 uF [T491D156M020AT]
15 uF [25TQC15MYFB]	15 uF [EEFHX1E150R]	15 uF [T489D156M025AT E300]	15 uF [T491D156M025AT]
15 uF [25TQC15MYFD]	15 uF [MDC10156K50A58 P7TUBE]	15 uF [T491A156M004AT]	15 uF [T491D156M035AT]
15 uF [A700V156M12RAT E040]	15 uF [MDC10156K50A58 P8TUBE]	15 uF [T491A156M006AT]	15 uF [T491S156M004AT]
15 uF [C1210C156K4PACT U]	15 uF [MMC16.5156K50C 31TR24]	15 uF [T491A156M010AT]	15 uF [T491S156M006AT]
15 uF [C1210C156K8PACT U]		15 uF [T491B156M004AT]	15 uF [T491T156M004AT]

Multisim 14.1 Base Edition Components

15 uF [T491T156M006AT]	15 uF [T494C156M010AT]	15 uF [T494U156M016AT]	15 uF [T495X156M035AT E200]
15 uF [T491T156M010AT]	15 uF [T494C156M016AT]	15 uF [T494X156M035AT]	15 uF [T495X156M050AT E200]
15 uF [T491U156M010AT]	15 uF [T494C156M020AT]	15 uF [T494X156M050AT]	15 uF [T495X156M050AT E300]
15 uF [T491U156M016AT]	15 uF [T494C156M025AT]	15 uF [T495B156M010AT E500]	15 uF [T497E156M010AT 6110]
15 uF [T491X156M035AT]	15 uF [T494D156M020AT]	15 uF [T495C156M010AT E375]	15 uF [T498B156M006AT E1K8]
15 uF [T491X156M050AT]	15 uF [T494D156M025AT]	15 uF [T495C156M010AT E400]	15 uF [T498B156M010AT E1K5]
15 uF [T494A156M004AT]	15 uF [T494D156M035AT]	15 uF [T495D156M020AT E275]	15 uF [T498C156M010AT E1K8]
15 uF [T494A156M006AT]	15 uF [T494S156M004AT]	15 uF [T495D156M025AT E100]	15 uF [T498C156M016AT E1K1]
15 uF [T494A156M010AT]	15 uF [T494S156M006AT]	15 uF [T495D156M025AT E275]	15 uF [T498D156M025AT E700]
15 uF [T494B156M004AT]	15 uF [T494T156M004AT]	15 uF [T495D156M035AT E225]	15 uF [T499B156M006AT E3K5]
15 uF [T494B156M006AT]	15 uF [T494T156M006AT]	15 uF [T495D156M035AT E300]	15 uF [T499D156M020AT E1K0]
15 uF [T494B156M010AT]	15 uF [T494T156M010AT]		
15 uF [T494B156M016AT]	15 uF [T494U156M010AT]		
15 uF [T494B156M025AT]			
15 uF [T494C156M006AT]			

Multisim 14.1 Base Edition Components

15 uF [T513D156M035AH 6110]	15 uF [T521X156M063AT E035]	15 uF [TAJC156K010RNJ]	15 uF [TAJT156K010RNJ]
15 uF [T520A156M010AT E080]	15 uF [T521X156M063AT E150]	15 uF [TAJC156K016RNJ]	15 uF [TAJW156K020RNJ]
15 uF [T520D156M025AT E060]	15 uF [T541X156M063AH 6510]	15 uF [TAJC156K020RNJ]	15 uF [TAJY156K025RNJ]
15 uF [T520D156M025AT E080]	15 uF [T543T156M006AT E100]	15 uF [TAJC156K035RNJ]	15 uF [THJB156K006RJJ]
15 uF [T520T156M004AT E100]	15 uF [TACR156K003RTA]	15 uF [TAJD156K020RNJ]	15 uF [THJB156K010RJJ]
15 uF [T520T156M006AT E100]	15 uF [TACR156K004RTA]	15 uF [TAJD156K025RNJ]	15 uF [THJC156K020RJJ]
15 uF [T520T156M12RAT E080]	15 uF [TACR156K006RTA]	15 uF [TAJD156K035RNJ]	15 uF [THJD156K035RJJ]
15 uF [T521B156M016AT E090]	15 uF [TACR156K010RTA]	15 uF [TAJD156K050RNJ]	15 uF [TPME156K050R00 75]
15 uF [T521V156M025AT E090]	15 uF [TAJA156K006RNJ]	15 uF [TAJE156K050RNJ]	15 uF [TPME156K050R01 00]
15 uF [T521V156M035AT E100]	15 uF [TAJA156K010RNJ]	15 uF [TAJP156K006RNJ]	15 uF [TPSA156K006R070 0]
15 uF [T521V156M035AT E100]	15 uF [TAJB156K006RNJ]	15 uF [TAJR156K004RNJ]	15 uF [TPSA156K006R150 0]
15 uF [T521V156M035AT E125]	15 uF [TAJB156K010RNJ]	15 uF [TAJS156K004RNJ]	15 uF [TPSA156K006R150 0]
	15 uF [TAJB156K016RNJ]	15 uF [TAJS156K006RNJ]	15 uF [TPSA156K010R100 0]
	15 uF [TAJB156K020RNJ]	15 uF [TAJT156K006RNJ]	

Multisim 14.1 Base Edition Components

15 uF [TPSB156K010R060 0]	15 uF [TPSV156K050R025 0]	15 uH [SDR0805- 150ML]	15 uH [SRN3015- 150M]
15 uF [TPSB156K016R080 0]	15 uF [TRJA156K010RRJ]	15 uH [SDR0906- 150ML]	15 uH [SRN4012T- 150M]
15 uF [TPSC156K016R070 0]	15 uF [TRJB156K016RRJ]	15 uH [SDR1005- 150ML]	15 uH [SRN4018- 150M]
15 uF [TPSC156K020R040 0]	15 uF [TRJB156K020RRJ]	15 uH [SDR1006- 150ML]	15 uH [SRN4026- 150M]
15 uF [TPSC156K020R040 0]	15 uF [TRJD156K035RRJ]	15 uH [SDR1030- 150M]	15 uH [SRN5020- 150M]
15 uF [TPSC156K020R045 0]	15 uH [SDE0403A- 150M]	15 uH [SDR1045- 150M]	15 uH [SRN5040- 150M]
15 uF [TPSC156K025R030 0]	15 uH [SDE0604A- 150M]	15 uH [SDR1105- 150ML]	15 uH [SRN6028- 150M]
15 uF [TPSC156K035R045 0]	15 uH [SDE0805A- 150M]	15 uH [SDR1305- 150M]	15 uH [SRN6045- 150M]
15 uF [TPSD156K025R010 0]	15 uH [SDE1006A- 150M]	15 uH [SDR1307- 150ML]	15 uH [SRN8040- 150M]
15 uF [TPSD156K025R030 0]	15 uH [SDR0302- 150ML]	15 uH [SDR1307A- 150M]	15 uH [SRP1038A- 150M]
15 uF [TPSD156K035R010 0]	15 uH [SDR0403- 150ML]	15 uH [SDR1806- 150ML]	15 uH [SRP1040- 150M]
15 uF [TPSD156K035R030 0]	15 uH [SDR0503- 150ML]	15 uH [SDR6603- 150M]	15 uH [SRP1265A- 150M]
15 uF [TPSD156K035R010 0]	15 uH [SDR0603- 150ML]	15 uH [SDR7030- 150M]	15 uH [SRP1770TA- 150M]
15 uF [TPSD156K035R030 0]	15 uH [SDR0604- 150YL]	15 uH [SDR7045- 150M]	15 uH [SRP4020TA- 150M]
	15 uH [SDR0703- 150KL]	15 uH [SRN3010- 150M]	15 uH [SRP6540- 150M]

Multisim 14.1 Base Edition Components

15 uH [SRP7050TA-150M]	15 uH [SRR1208-150ML]	15 uH [SRR6038-150Y]	15 uH [SRU2016-150Y]
15 uH [SRR0603-150ML]	15 uH [SRR1210-150M]	15 uH [SRR6040A-150M]	15 uH [SRU3014-150Y]
15 uH [SRR0604-150ML]	15 uH [SRR1210A-150M]	15 uH [SRR6603-150ML]	15 uH [SRU3017-150Y]
15 uH [SRR0618-150ML]	15 uH [SRR1240-150M]	15 uH [SRR7032-150M]	15 uH [SRU3028-150Y]
15 uH [SRR0735A-150M]	15 uH [SRR1260-150M]	15 uH [SRR7045-150M]	15 uH [SRU3028A-150Y]
15 uH [SRR0745A-150M]	15 uH [SRR1260A-150M]	15 uH [SRU1028-150Y]	15 uH [SRU5011-150Y]
15 uH [SRR0804-150M]	15 uH [SRR1280-150M]	15 uH [SRU1028A-150Y]	15 uH [SRU5016-150Y]
15 uH [SRR0805-150M]	15 uH [SRR1806-150M]	15 uH [SRU1038-150Y]	15 uH [SRU5018-150Y]
15 uH [SRR0905-150M]	15 uH [SRR3011-150YL]	15 uH [SRU1038A-150Y]	15 uH [SRU5028-150Y]
15 uH [SRR0906-150ML]	15 uH [SRR4011-150YL]	15 uH [SRU1048-150Y]	15 uH [SRU5028A-150Y]
15 uH [SRR0908-150ML]	15 uH [SRR4018-150Y]	15 uH [SRU1048A-150Y]	15 uH [SRU6011-150Y]
15 uH [SRR1003-150M]	15 uH [SRR4028-150Y]	15 uH [SRU1063-150Y]	15 uH [SRU6018-150Y]
15 uH [SRR1005-150M]	15 uH [SRR5018-150Y]	15 uH [SRU2009-150Y]	15 uH [SRU6025-150Y]
15 uH [SRR1205-150ML]	15 uH [SRR5028-150Y]	15 uH [SRU2011-150Y]	15 uH [SRU6025A-150Y]
15 uH [SRR1206-150ML]	15 uH [SRR6028-150Y]	15 uH [SRU2013-150Y]	15 uH [SRU8028-150Y]

Multisim 14.1 Base Edition Components

15 uH [SRU8028A-150Y]	15.4 Ohm [CR1206-FX-15R4ELF]	150 kOhm [4114R-2-154LF]	150 kOhm [4309R-101-154]
15 uH [SRU8043-150Y]	15.8 kOhm [CR0402-FX-1582GLF]	150 kOhm [4116R-1-154]	150 kOhm [4309R-101-154LF]
15.4 kOhm [CR0402-FX-1542GLF]	15.8 kOhm [CR0603-FX-1582ELF]	150 kOhm [4116R-1-154LF]	150 kOhm [4310H-102-154]
15.4 kOhm [CR0603-FX-1542ELF]	15.8 kOhm [CR0805-FX-1582ELF]	150 kOhm [4116R-2-154]	150 kOhm [4310R-101-154]
15.4 kOhm [CR0805-FX-1542ELF]	15.8 kOhm [CR1206-FX-1582ELF]	150 kOhm [4116R-2-154LF]	150 kOhm [4310R-101-154LF]
15.4 kOhm [CR1206-FX-1542ELF]	15.8 kOhm [CRT0603-BY-1582ELF]	150 kOhm [4306R-101-154]	150 kOhm [4310R-102-154]
15.4 kOhm [CRT0402-FZ-1542GLF]	15.8 kOhm [CRT1206-DY-1582ELF]	150 kOhm [4306R-101-154LF]	150 kOhm [4310R-102-154LF]
15.4 kOhm [CRT0805-BY-1542ELF]	15.8 Ohm [CR0805-FX-15R8ELF]	150 kOhm [4306R-102-154]	150 kOhm [4604X-102-154LF]
15.4 kOhm [CRT1206-BY-1542ELF]	15.8 Ohm [CR1206-FX-15R8ELF]	150 kOhm [4306R-102-154LF]	150 kOhm [4606X-101-154LF]
15.4 kOhm [CRT1206-FZ-1542ELF]	15 AMP	150 kOhm [4308M-102-154]	150 kOhm [4606X-102-154LF]
15.4 Ohm [CR0402-FX-15R4GLF]	150 kOhm [4114R-1-154]	150 kOhm [4308M-102-154LF]	150 kOhm [4606X-AP2-154LF]
15.4 Ohm [CR0603-FX-15R4ELF]	150 kOhm [4114R-1-154LF]	150 kOhm [4308R-101-154]	150 kOhm [4607M-101-154LF]
	150 kOhm [4114R-2-154]	150 kOhm [4308R-101-154LF]	150 kOhm [4608M-101-154LF]
	150 kOhm [4114R-2-154LF]	150 kOhm [4308R-102-154]	150 kOhm [4608X-101-154LF]
	150 kOhm [4114R-2-154]	150 kOhm [4308R-102-154LF]	150 kOhm [4608X-102-154LF]

Multisim 14.1 Base Edition Components

150 kOhm [4608X-AP2-154LF]	150 kOhm [4816P-2-154]	150 kOhm [CAY16-154J8LF]	150 kOhm [CR1206-JW-154ELF]
150 kOhm [4609X-101-154LF]	150 kOhm [4816P-2-154LF]	150 kOhm [CHV1206-FW-1503ELF]	150 kOhm [CR2512-JW-154ELF]
150 kOhm [4610H-102-154LF]	150 kOhm [4816P-T01-154]	150 kOhm [CHV1206-JW-154ELF]	150 kOhm [CRM1206-FX-1503ELF]
150 kOhm [4610X-101-154LF]	150 kOhm [4816P-T01-154LF]	150 kOhm [CHV2010-JW-154ELF]	150 kOhm [CRM2512-JW-154ELF]
150 kOhm [4610X-102-154LF]	150 kOhm [4816P-T02-154]	150 kOhm [CR0402-FX-1503GLF]	150 kOhm [CRT0402-BY-1503GLF]
150 kOhm [4611X-101-154LF]	150 kOhm [4816P-T02-154LF]	150 kOhm [CR0402-JW-154GLF]	150 kOhm [CRT0805-BY-1503EAS]
150 kOhm [4612X-102-154LF]	150 kOhm [4820P-T02-154]	150 kOhm [CR0603-FX-1503ELF]	150 kOhm [CRT0805-BY-1503ELF]
150 kOhm [4814P-1-154]	150 kOhm [CAT16-1503F4LF]	150 kOhm [CR0603-JW-154ELF]	150 mOhm [CRL0603-FW-R150ELF]
150 kOhm [4814P-2-154]	150 kOhm [CAT16-1503F8LF]	150 kOhm [CR0805-FX-1503ELF]	150 mOhm [CRL0603-JW-R150ELF]
150 kOhm [4814P-2-154LF]	150 kOhm [CAT16-154J4LF]	150 kOhm [CR0805-JW-154ELF]	150 mOhm [CRL0805-FW-R150ELF]
150 kOhm [4814P-T01-154]	150 kOhm [CAT25-154JALF]	150 kOhm [CR1206-FX-1503ELF]	150 mOhm [CRL0805-JW-R150ELF]
150 kOhm [4814P-T02-154]	150 kOhm [CAY10-154J2LF]		
150 kOhm [4814P-T02-154LF]	150 kOhm [CAY10-154J4LF]		
150 kOhm [4816P-1-154]	150 kOhm [CAY16-1503F4LF]		
150 kOhm [4816P-1-154LF]	150 kOhm [CAY16-154J4LF]		

Multisim 14.1 Base Edition Components

150 mOhm [CRL1206-FW- R150ELF]	150 mOhm [PWR1913WR150J]	150 nF [06125C154KAT2W]	150 nF [C0805C154M3VAC TU]
150 mOhm [CRL1206-JW- R150ELF]	150 mOhm [PWR1913WR150JE]	150 nF [C0603C154K4RACT U]	150 nF [C1206C154K1RACT U]
150 mOhm [CRL2010-FW- R150ELF]	150 mOhm [PWR220T-35- R150F]	150 nF [C0603C154K5RACT U]	150 nF [C1206C154K2RACT U]
150 mOhm [CRL2010-JW- R150ELF]	150 mOhm [PWR221T-30- R150F]	150 nF [C0603C154K8RACT U]	150 nF [C1206C154K3RACT U]
150 mOhm [CRL2512-FW- R150ELF]	150 mOhm [PWR2615NR150JE]	150 nF [C0603C154M3VAC TU]	150 nF [C1206C154K4RACT U]
150 mOhm [CRL2512-JW- R150ELF]	150 mOhm [PWR2615WR150J]	150 nF [C0603C154M4VAC TU]	150 nF [C1206C154K5RACT U]
150 mOhm [CRM1206-FX- R150ELF]	150 mOhm [PWR4525WR150J]	150 nF [C0603C154M8VAC TU]	150 nF [C1206C154M5UAC TU]
150 mOhm [CRM1206-JX- R150ELF]	150 mOhm [PWR4525WR150JE]	150 nF [C0805C154K3RACT U]	150 nF [C1206F154K1RACT U]
150 mOhm [CRM2010-FX- R150ELF]	150 mOhm [PWR6327WR150J]	150 nF [C0805C154K4RACT U]	150 nF [C1206F154K3RACT U]
150 mOhm [CRM2512-FX- R150ELF]	150 mOhm [PWR6327WR150JE]	150 nF [C0805C154K5RACT U]	150 nF [C1206F154K4RACT U]
150 mOhm [PWR163S-25- R150FE]	150 nF [06123C154KAT2W]	150 nF [C0805C154K8RACT U]	150 nF [C1206F154K5RACT U]

Multisim 14.1 Base Edition Components

150 nF [C1210C154K1RACT U]	150 nF [C1812C154K2RACT U]	150 nF [C1825C154K5RACT U]	150 nF [MDC10154K630A5 8P7TUBE]
150 nF [C1210C154K3HACT U]	150 nF [C1812C154K5GACT U]	150 nF [C2220C154K1GACT U]	150 nF [MDC10154K630A5 8P8TUBE]
150 nF [C1210C154K5HACT U]	150 nF [C1812C154K5HACT U]	150 nF [C2220C154K5GACT U]	150 nF [MDC15154K100B5 3P3TUBE]
150 nF [C1210C154K5RACT U]	150 nF [C1812C154K5RACT U]	150 nF [C2225C154K1RACT U]	150 nF [MDC15154K250B5 3P3TUBE]
150 nF [C1210F154K1RACT U]	150 nF [C1812C154M1UAC TU]	150 nF [C2225C154K2RACT U]	150 nF [MDC15154K400B5 3P3TUBE]
150 nF [C1210F154K3RACT U]	150 nF [C1812C154M5UAC TU]	150 nF [GMC5.7154K50J35 TR12]	150 nF [MDC15154K50B53 P3TUBE]
150 nF [C1210F154K4RACT U]	150 nF [C1812F154K1RACT U]	150 nF [GMC7.3154K63K31 TR12]	150 nF [MDK10154K100A5 2P3TUBE]
150 nF [C1210F154K5RACT U]	150 nF [C1812F154K2RACT U]	150 nF [MDC10154K100A5 2P3TUBE]	150 nF [MDK10154K250A5 2P3TUBE]
150 nF [C1812C154K1GACT U]	150 nF [C1812F154K3RACT U]	150 nF [MDC10154K250A5 2P3TUBE]	150 nF [MDK10154K400A5 2P3TUBE]
150 nF [C1812C154K1HACT U]	150 nF [C1812F154K5RACT U]	150 nF [MDC10154K400A5 2P3TUBE]	150 nF [MDK10154K50A52 P3TUBE]
150 nF [C1812C154K1RACT U]	150 nF [C1825C154K1RACT U]	150 nF [MDC10154K50A52 P3TUBE]	150 nF [MDK15154K400B5 3P3TUBE]

Multisim 14.1 Base Edition Components

150 nF [MDS10154K100A5 2P3TUBE]	150 nF [T429A154M050AH 4250]	150 nF [TRJA154K035RRJ]	150 Ohm [4306M- 101-151]
150 nF [MDS10154K250A5 2P3TUBE]	150 nF [T491A154M035AT]	150 nH [SRP1040- R15M]	150 Ohm [4306M- 101-151LF]
150 nF [MDS10154K400A5 2P3TUBE]	150 nF [T491A154M050AT]	150 nH [SRP1235- R15M]	150 Ohm [4306R- 101-151]
150 nF [MDS10154K50A52 P3TUBE]	150 nF [T491B154M050AT]	150 nH [SRP5015TA-R15Y]	150 Ohm [4306R- 101-151LF]
150 nF [MDS10154K50A52 P3TUBE]	150 nF [T494A154M035AT]	150 nH [SRP7030- R15FM]	150 Ohm [4306R- 102-151]
150 nF [MDS15154K100B5 3P3TUBE]	150 nF [T494A154M050AT]	150 Ohm [4108R-1- 151LF]	150 Ohm [4306R- 102-151LF]
150 nF [MDS15154K250B5 3P3TUBE]	150 nF [T494B154M050AT]	150 Ohm [4114R-1- 151]	150 Ohm [4308H- 101-151]
150 nF [MMC5.7154K50J3 3TR12]	150 nF [TAJA154K035RNJ]	150 Ohm [4114R-1- 151LF]	150 Ohm [4308H- 102-151]
150 nF [MMC7.3154K50K3 1TR12]	150 nF [TAJA154K050RNJ]	150 Ohm [4114R-2- 151]	150 Ohm [4308M- 101-151]
150 nF [MMC7.3154K50K3 1TR12]	150 nF [TAJB154K050RNJ]	150 Ohm [4114R-2- 151LF]	150 Ohm [4308R- 101-151]
150 nF [SPC12.7154K100B 31TR24]	150 nF [TAJR154K020RNJ]	150 Ohm [4116R-1- 151]	150 Ohm [4308R- 101-151LF]
150 nF [SPC12.7154K100B 31TR24]	150 nF [TAJS154K020RNJ]	150 Ohm [4116R-1- 151LF]	150 Ohm [4308R- 102-151]
150 nF [SPC16.5154K250C 31TR24]	150 nF [TAJS154K035RNJ]	150 Ohm [4116R-2- 151]	150 Ohm [4308R- 102-151LF]
150 nF [SPC16.5154K400C 31TR24]	150 nF [THJA154K035RJN]	150 Ohm [4116R-2- 151LF]	150 Ohm [4309R- 101-151]
	150 nF [TPSA154K050R900 0]	150 Ohm [4304M- 102-151]	150 Ohm [4309R- 101-151LF]

Multisim 14.1 Base Edition Components

150 Ohm [4310H-101-151]	150 Ohm [4420P-T02-151]	150 Ohm [4609M-101-151LF]	150 Ohm [4814P-T01-151LF]
150 Ohm [4310H-101-151LF]	150 Ohm [4604X-101-151LF]	150 Ohm [4609X-101-151LF]	150 Ohm [4814P-T02-151]
150 Ohm [4310H-102-151]	150 Ohm [4604X-102-151LF]	150 Ohm [4609X-AP1-151LF]	150 Ohm [4814P-T02-151LF]
150 Ohm [4310M-101-151]	150 Ohm [4605X-101-151LF]	150 Ohm [4610M-101-151LF]	150 Ohm [4816P-1-151]
150 Ohm [4310R-101-151]	150 Ohm [4606H-101-151LF]	150 Ohm [4610X-101-151LF]	150 Ohm [4816P-1-151LF]
150 Ohm [4310R-101-151LF]	150 Ohm [4606H-102-151LF]	150 Ohm [4610X-102-151LF]	150 Ohm [4816P-2-151]
150 Ohm [4310R-102-151]	150 Ohm [4606X-101-151LF]	150 Ohm [4610X-AP2-151LF]	150 Ohm [4816P-2-151LF]
150 Ohm [4310R-102-151LF]	150 Ohm [4606X-102-151LF]	150 Ohm [4612X-101-151LF]	150 Ohm [4816P-T01-151]
150 Ohm [4416P-1-151]	150 Ohm [4607M-101-151LF]	150 Ohm [4612X-102-151LF]	150 Ohm [4816P-T01-151LF]
150 Ohm [4416P-2-151]	150 Ohm [4607X-101-151LF]	150 Ohm [4614X-102-151LF]	150 Ohm [4816P-T02-151]
150 Ohm [4416P-T01-151]	150 Ohm [4608M-101-151LF]	150 Ohm [4814P-1-151]	150 Ohm [4816P-T02-151LF]
150 Ohm [4416P-T02-151]	150 Ohm [4608M-102-151LF]	150 Ohm [4814P-1-151LF]	150 Ohm [4818P-T02-151]
150 Ohm [4420P-1-151]	150 Ohm [4608X-101-151LF]	150 Ohm [4814P-2-151]	150 Ohm [4818P-T02-151LF]
150 Ohm [4420P-2-151]	150 Ohm [4608X-102-151LF]	150 Ohm [4814P-2-151LF]	150 Ohm [4820P-1-151]
150 Ohm [4420P-T01-151]	150 Ohm [4608X-AP2-151LF]	150 Ohm [4814P-T01-151]	150 Ohm [4820P-T01-151]

Multisim 14.1 Base Edition Components

150 Ohm [4820P-T02-151]	150 Ohm [CR0603-FX-1500ELF]	150 Ohm [CRM2010-JW-151ELF]	150 Ohm [PWR2615W1500JE]
150 Ohm [CAT10-151J4LF]	150 Ohm [CR0603-FX-1500HLF]	150 Ohm [CRM2512-FX-1500ELF]	150 Ohm [PWR263S-20-1500JE]
150 Ohm [CAT16-1500F4LF]	150 Ohm [CR0603-JW-151ELF]	150 Ohm [CRM2512-JW-151ELF]	150 Ohm [PWR263S-35-1500FE]
150 Ohm [CAT16-151J4LF]	150 Ohm [CR0805-FX-1500ELF]	150 Ohm [CRT0603-BY-1500ELF]	150 Ohm [PWR263S-35-1500J]
150 Ohm [CAT16-151J8LF]	150 Ohm [CR0805-FX-1500GLF]	150 Ohm [CRT0805-BY-1500ELF]	150 Ohm [PWR4525W1500J]
150 Ohm [CAT25-151JALF]	150 Ohm [CR1206-FX-1500ELF]	150 Ohm [CRT0805-DY-1500ELF]	150 Ohm [PWR4525W1500JE]
150 Ohm [CAY10-151J4LF]	150 Ohm [CR1206-JW-151ELF]	150 Ohm [PWR163S-25-1500FE]	150 Ohm [PWR5322W1500JE]
150 Ohm [CAY16-151J4LF]	150 Ohm [CR2010-FX-1500ELF]	150 Ohm [PWR220T-20-1500F]	150 Ohm [PWR6327W1500J]
150 Ohm [CAY16-151J8LF]	150 Ohm [CR2512-FX-1500ELF]	150 Ohm [PWR220T-35-1500F]	150 Ohm [PWR6327W1500JE]
150 Ohm [CAY17-151JALF]	150 Ohm [CR2512-JW-151ELF]	150 Ohm [PWR221T-30-1500F]	150 Ohm [WS1M1500J]
150 Ohm [CR0201-FW-1500GLF]	150 Ohm [CRM1206-FX-1500ELF]	150 Ohm [PWR2615W1500J]	150 pF [C0402C151K1HACTU]
150 Ohm [CR0402-FX-1500GLF]	150 Ohm [CRM2010-FX-1500ELF]		

Multisim 14.1 Base Edition Components

150 pF [C0402C151K3HACT U]	150 pF [C0805C151K1GACT U]	150 pF [C1825C151KBGAC TU]	150 uF [6SVPE150M]
150 pF [C0402C151K3RACT U]	150 pF [C0805C151K2GACT U]	150 pF [C2220C151KBGAC TU]	150 uF [6TPC150M]
150 pF [C0402C151K4RACT U]	150 pF [C0805C151K3GACT U]	150 pF [C2225C151KBGAC TU]	150 uF [6TPE150MAPB]
150 pF [C0402C151K5GACT U]	150 pF [C0805C151K4GACT U]	150 pF [CA064C151K4GAC TU]	150 uF [6TPE150MAZB]
150 pF [C0402C151K5HACT U]	150 pF [C0805C151K5GACT U]	150 pF [CA064C151K5GAC TU]	150 uF [6TPE150MI]
150 pF [C0402C151K5RACT U]	150 pF [C1206C151K1GACT U]	150 uF [10TPB150ML]	150 uF [6TPG150M]
150 pF [C0402C151K8RACT U]	150 pF [C1206C151K2GACT U]	150 uF [10TPF150ML]	150 uF [6TPG150MZG]
150 pF [C0603C151K1GACT U]	150 pF [C1206C151K5GACT U]	150 uF [16SVPC150M]	150 uF [6TPU150MBI]
150 pF [C0603C151K3GACT U]	150 pF [C1206C151KBGAC TU]	150 uF [16TQC150MYF]	150 uF [8TPC150M]
150 pF [C0603C151K4GACT U]	150 pF [C1210C151KBGAC TU]	150 uF [4SVPC150MY]	150 uF [A700D157M004AT E015]
150 pF [C0603C151K5GACT U]	150 pF [C1812C151KBGAC TU]	150 uF [4TPE150MAZB]	150 uF [A700D157M004AT E018]
		150 uF [4TPE150MI]	150 uF [A700D157M2R5AT E015]
		150 uF [4TPH150MABC]	

Multisim 14.1 Base Edition Components

150 uF [A700D157M2R5AT E018]	150 uF [EEFSX0E151ER]	150 uF [T491D157M010AT]	150 uF [T494D157M010AT]
150 uF [A700V157M002AT E009]	150 uF [EEFSX0G151E7] 150 uF [EEFSX0G151ER]	150 uF [T491D157M016AT]	150 uF [T494D157M016AT]
150 uF [A700V157M002AT E018]	150 uF [EEFSX0J151ER]	150 uF [T491V157M004AT]	150 uF [T494V157M004AT]
150 uF [A700V157M002AT E025]	150 uF [EEHZA1V151P]	150 uF [T491V157M006AT]	150 uF [T494V157M006AT]
150 uF [A700V157M002AT E028]	150 uF [EEHZC1V151P]	150 uF [T491V157M010AT]	150 uF [T494V157M010AT]
150 uF [A700X157M006AT E010]	150 uF [T429G157M006AH 4250]	150 uF [T491X157M010AT]	150 uF [T494X157M010AT]
150 uF [A700X157M006AT E015]	150 uF [T429X157M010AH 4250]	150 uF [T491X157M016AT]	150 uF [T494X157M016AT]
150 uF [A700X157M010AT E010]	150 uF [T491B157M004AT]	150 uF [T494B157M004AT]	150 uF [T495B157M004AT E900]
150 uF [A700X157M010AT E015]	150 uF [T491C157M004AT]	150 uF [T494C157M004AT]	150 uF [T495C157M006AT E200]
150 uF [A700X157M010AT E015]	150 uF [T491C157M006AT]	150 uF [T494C157M006AT]	150 uF [T495D157M006AT E050]
150 uF [EEFCX0G151R]	150 uF [T491D157M004AT]	150 uF [T494D157M004AT]	150 uF [T495D157M006AT E125]
150 uF [EEFCX0J151R]	150 uF [T491D157M006AT]	150 uF [T494D157M006AT]	150 uF [T495D157M010AT E050]

Multisim 14.1 Base Edition Components

150 uF [T495D157M010AT E060]	150 uF [T495X157M016AT E100]	150 uF [T520B157M004AT E025]	150 uF [T520C157M004AT E100]
150 uF [T495D157M010AT E100]	150 uF [T510X157M016AT E030]	150 uF [T520B157M004AT E030]	150 uF [T520C157M006AT E015]
150 uF [T495D157M016AT E060]	150 uF [T510X157M016AT E040]	150 uF [T520B157M004AT E035]	150 uF [T520C157M006AT E025]
150 uF [T495D157M016AT E085]	150 uF [T513X157M016AH 6110]	150 uF [T520B157M004AT E040]	150 uF [T520C157M006AT E045]
150 uF [T495D157M016AT E100]	150 uF [T513X157M016AH 6120]	150 uF [T520B157M004AT E070]	150 uF [T520C157M006AT E055]
150 uF [T495D157M016AT E125]	150 uF [T520B157M003AT E025]	150 uF [T520B157M006AT E035]	150 uF [T520C157M010AT E055]
150 uF [T495D157M016AT E150]	150 uF [T520B157M003AT E035]	150 uF [T520B157M006AT E045]	150 uF [T520D157M004AT E007]
150 uF [T495V157M010AT E150]	150 uF [T520B157M003AT E040]	150 uF [T520B157M006AT E070]	150 uF [T520D157M006AT E006]
150 uF [T495X157M010AT E085]	150 uF [T520B157M003AT E070]	150 uF [T520C157M004AT E015]	150 uF [T520D157M006AT E007]
150 uF [T495X157M010AT E100]	150 uF [T520B157M004AT E015]	150 uF [T520C157M004AT E025]	150 uF [T520D157M006AT E015]
150 uF [T495X157M016AT E075]	150 uF [T520B157M004AT E018]	150 uF [T520C157M004AT E045]	150 uF [T520D157M006AT E025]

Multisim 14.1 Base Edition Components

150 uF [T520D157M006AT E055]	150 uF [T520U157M006AT E045]	150 uF [T520V157M006AT E012]	150 uF [T522V157M006AT E040]
150 uF [T520D157M008AT E025]	150 uF [T520U157M006AT E055]	150 uF [T520V157M006AT E015]	150 uF [T525B157M003AT E080]
150 uF [T520D157M008AT E040]	150 uF [T520U157M2R5AT E055]	150 uF [T520V157M006AT E018]	150 uF [T525D157M006AT E025]
150 uF [T520D157M008AT E055]	150 uF [T520V157M004AT E007]	150 uF [T520V157M006AT E025]	150 uF [T525D157M010AT E025]
150 uF [T520D157M010AT E025]	150 uF [T520V157M004AT E009]	150 uF [T520V157M006AT E040]	150 uF [T528Z157M006AT E007]
150 uF [T520D157M010AT E040]	150 uF [T520V157M004AT E012]	150 uF [T520V157M006AT E045]	150 uF [T528Z157M006AT E008]
150 uF [T520D157M010AT E055]	150 uF [T520V157M004AT E015]	150 uF [T520V157M010AT E018]	150 uF [T528Z157M006AT E009]
150 uF [T520L157M006AT E012]	150 uF [T520V157M004AT E025]	150 uF [T520V157M010AT E040]	150 uF [T528Z157M006AT E012]
150 uF [T520L157M006AT E025]	150 uF [T520V157M006AT E006]	150 uF [T520W157M006AT E025]	150 uF [T530D157M010AT E006]
150 uF [T520M157M006AT E070]	150 uF [T520V157M006AT E007]	150 uF [T520W157M006AT E040]	150 uF [T530D157M010AT E010]
150 uF [T520U157M004AT E055]	150 uF [T520V157M006AT E009]	150 uF [T520X157M016AT E040]	150 uF [T530X157M016AT E015]

Multisim 14.1 Base Edition Components

150 uF [T530X157M016AT E025]	150 uF [TAJX157K006RNJ]	150 uF [TPSC157K006R025 0]	150 uF [TPSV157K016R007 5]
150 uF [T530X157M016AT E040]	150 uF [TAJY157K006RNJ]	150 uF [TPSD157K006R005 0]	150 uF [TPSV157K020R008 0]
150 uF [TAJB157K002RNJ]	150 uF [THJD157K006RJN]	150 uF [TPSD157K006R012 5]	150 uF [TPSY157K006R004 0]
150 uF [TAJB157K004RNJ]	150 uF [TPME157K016R00 30]	150 uF [TPSD157K010R005 0]	150 uF [TPSY157K010R010 0]
150 uF [TAJC157K006RNJ]	150 uF [TPME157K016R00 40]	150 uF [TPSD157K010R008 5]	150 uF [TPSY157K010R015 0]
150 uF [TAJD157K006RNJ]	150 uF [TPME157K020R00 35]	150 uF [TPSD157K010R010 0]	150 uF [TPSY157K010R020 0]
150 uF [TAJD157K010RNJ]	150 uF [TPSB157K002R015 0]	150 uF [TPSD157K016R010 0]	150 uF [TRJC157K006RRJ]
150 uF [TAJD157K016RNJ]	150 uF [TPSC157K006R005 0]	150 uF [TPSD157K016R012 5]	150 uF [TRJD157K010RRJ]
150 uF [TAJE157K010RNJ]	150 uF [TPSC157K006R009 0]	150 uF [TPSD157K016R015 0]	150 uF [TRJE157K010RRJ]
150 uF [TAJE157K016RNJ]	150 uF [TPSC157K006R015 0]	150 uF [TPSE157K016R010 0]	150 uF [TRME157K016R00 30]
150 uF [TAJE157K020RNJ]	150 uF [TPSC157K006R020 0]	150 uF [TPSV157K016R004 5]	150 uF [TRME157K016R00 40]
150 uF [TAJF157K010RNJ]			
150 uF [TAJV157K016RNJ]			
150 uF [TAJV157K020RNJ]			

Multisim 14.1 Base Edition Components

150 uH [SDE0604A-151K]	150 uH [SDR1105-151KL]	150 uH [SRR0804-151K]	150 uH [SRR1280-151K]
150 uH [SDE0805A-151K]	150 uH [SDR1305-151K]	150 uH [SRR0805-151K]	150 uH [SRR1806-151M]
150 uH [SDE1006A-151K]	150 uH [SDR1307-151KL]	150 uH [SRR0905-151K]	150 uH [SRR4011-151YL]
150 uH [SDR0302-151KL]	150 uH [SDR1307A-151K]	150 uH [SRR0906-151YL]	150 uH [SRR4018-151Y]
150 uH [SDR0403-151KL]	150 uH [SDR1806-151KL]	150 uH [SRR0908-151YL]	150 uH [SRR4028-151Y]
150 uH [SDR0503-151KL]	150 uH [SDR6603-151M]	150 uH [SRR1003-151M]	150 uH [SRR5018-151Y]
150 uH [SDR0603-151KL]	150 uH [SDR7030-151K]	150 uH [SRR1005-151K]	150 uH [SRR5028-151Y]
150 uH [SDR0604-151KL]	150 uH [SDR7045-151K]	150 uH [SRR1205-151KL]	150 uH [SRR6028-151Y]
150 uH [SDR0703-151KL]	150 uH [SRN1060-151M]	150 uH [SRR1206-151KL]	150 uH [SRR6603-151ML]
150 uH [SDR0805-151KL]	150 uH [SRN4018-151M]	150 uH [SRR1208-151YL]	150 uH [SRR7032-151M]
150 uH [SDR0906-151KL]	150 uH [SRN4026-151M]	150 uH [SRR1210-151M]	150 uH [SRR7045-151M]
150 uH [SDR1005-151KL]	150 uH [SRR0603-151KL]	150 uH [SRR1210A-151M]	150 uH [SRU1028-151Y]
150 uH [SDR1006-151KL]	150 uH [SRR0604-151KL]	150 uH [SRR1240-151K]	150 uH [SRU1028A-151Y]
150 uH [SDR1030-151K]	150 uH [SRR0735A-151M]	150 uH [SRR1260-151K]	150 uH [SRU1038-151Y]
150 uH [SDR1045-151K]	150 uH [SRR0745A-151M]	150 uH [SRR1260A-151K]	150 uH [SRU1038A-151Y]

Multisim 14.1 Base Edition Components

150 uH [SRU1048-151Y]	154 Ohm [CR0603-FX-1540ELF]	16 kOhm [4116R-1-163]	16 Ohm [CAT16-160J8LF]
150 uH [SRU1048A-151Y]	154 Ohm [CR0805-FX-1540ELF]	16 kOhm [4604X-102-163LF]	16 Ohm [CAY16-160J4LF]
150 uH [SRU6025-151Y]	154 Ohm [CR1206-FX-1540ELF]	16 kOhm [CAT16-163J4LF]	16 Ohm [CR0402-FX-16R0GLF]
150 uH [SRU6025A-151Y]	158 kOhm [CR0402-FX-1583GLF]	16 kOhm [CAY16-163J4LF]	16 Ohm [CR0603-FX-16R0ELF]
1-534206-0	158 kOhm [CR0603-FX-1583ELF]	16 kOhm [CR0402-FX-1602GLF]	16 Ohm [CR0603-JW-160ELF]
1-534206-3	158 kOhm [CR0603-FX-1583GLF]	16 kOhm [CR0603-FX-1602ELF]	16 Ohm [CR0805-FX-16R0ELF]
1-534206-7	158 kOhm [CR0603-FX-1583GLF]	16 kOhm [CR0603-JW-163ELF]	16 Ohm [CR0805-JW-160ELF]
154 kOhm [CR0402-FX-1543GLF]	158 kOhm [CR0805-FX-1583ELF]	16 kOhm [CR0805-FX-1602ELF]	16 Ohm [CR1206-FX-16R0ELF]
154 kOhm [CR0603-FX-1543ELF]	158 kOhm [CR1206-FX-1583ELF]	16 kOhm [CR0805-JW-163ELF]	16 Ohm [CR1206-JW-160ELF]
154 kOhm [CR0805-FX-1543ELF]	158 kOhm [CRT0805-BY-1583ELF]	16 kOhm [CR1206-FX-1602ELF]	16 Ohm [CRM2512-JW-160ELF]
154 kOhm [CR1206-FX-1543ELF]	158 Ohm [CR0603-FX-1580ELF]	16 kOhm [CRT0402-BY-1602GLF]	16 Ohm [CRT0805-BW-16R0ELF]
154 kOhm [CRT1206-BY-1543ELF]	158 Ohm [CR0805-FX-1580ELF]	16 kOhm [CRT0402-BZ-1602GLF]	16 pF [C0603C160K2GACT U]
154 kOhm [CRT1206-FZ-1543ELF]	158 Ohm [CR1206-FX-1580ELF]	16 Ohm [CAT10-160J4LF]	16 pF [C0603C160K5GACT U]
154 Ohm [CR0402-FX-1540GLF]	15C02MH-TL-E	16 Ohm [CAT16-160J4LF]	16 pF [C0805C160KBGAC TU]

Multisim 14.1 Base Edition Components

16 pF [C1206C160KBGAC TU]	16.2 kOhm [CRM2010-FX- 1622ELF]	16.5 kOhm [CRT0805-CX- 1652ELF]	16.9 Ohm [CR0402- FX-16R9GLF]
16 pF [C1210C160KBGAC TU]	16.2 kOhm [CRT0402-FZ- 1622GLF]	16.5 Ohm [CR0402- FX-16R5GLF]	16.9 Ohm [CR0603- FX-16R9ELF]
16 pF [C1812C160KBGAC TU]	16.2 kOhm [CRT0603-BY- 1622ELF]	16.5 Ohm [CR0603- FX-16R5ELF]	16.9 Ohm [CR0805- FX-16R9ELF]
16 pF [C1825C160KBGAC TU]	16.2 Ohm [CR0402- FX-16R2GLF]	16.5 Ohm [CR1206- FX-16R5ELF]	160 kOhm [CAT16- 1603F4LF]
16 pF [C2220C160KBGAC TU]	16.2 Ohm [CR0603- FX-16R2ELF]	16.9 kOhm [CR0402-FX- 1692GLF]	160 kOhm [CAY16- 164J4LF]
16 pF [C2225C160KBGAC TU]	16.2 Ohm [CR0805- FX-16R2ELF]	16.9 kOhm [CR0603-FX- 1692ELF]	160 kOhm [CR0402-FX- 1603GLF]
16.2 kOhm [CAY16- 1622F4LF]	16.2 Ohm [CR1206- FX-16R2ELF]	16.9 kOhm [CR0603-FX- 1692ELF]	160 kOhm [CR0603-FX- 1603ELF]
16.2 kOhm [CR0402-FX- 1622GLF]	16.2 Ohm [CRT0402-FZ- 16R2GLF]	16.9 kOhm [CR0805-FX- 1692ELF]	160 kOhm [CR0603-JW- 164ELF]
16.2 kOhm [CR0603-FX- 1622ELF]	16.5 kOhm [CR0402-FX- 1652GLF]	16.9 kOhm [CR1206-FX- 1692ELF]	160 kOhm [CR0805-FX- 1603ELF]
16.2 kOhm [CR0805-FX- 1622ELF]	16.5 kOhm [CR0603-FX- 1652ELF]	16.9 kOhm [CRT0603-BY- 1692ELF]	160 kOhm [CR0805-JW- 164ELF]
16.2 kOhm [CR1206-FX- 1622ELF]	16.5 kOhm [CR0805-FX- 1652ELF]	16.9 kOhm [CRT0805-BY- 1692ELF]	160 kOhm [CR1206-FX- 1603ELF]
			160 kOhm [CR1206-JW- 164ELF]

Multisim 14.1 Base Edition Components

160 kOhm [CRT0402-BY- 1603GLF]	160 mOhm [CRL2512-JW- R160ELF]	160 Ohm [CAT25- 161JALF]	160 pF [C0402C161K1HACT U]
160 kOhm [CRT0805-BY- 1603ELF]	160 mOhm [CRM1206-FX- R160ELF]	160 Ohm [CAY10- 161J4LF]	160 pF [C0402C161K3HACT U]
160 mOhm [CRL0603-FW- R160ELF]	160 mOhm [CRM1206-JX- R160ELF]	160 Ohm [CAY16- 1600F4LF]	160 pF [C0402C161K5HACT U]
160 mOhm [CRL0603-JW- R160ELF]	160 Ohm [4114R-1- 161]	160 Ohm [CAY16- 161J8LF]	160 pF [C0805C161K3GACT U]
160 mOhm [CRL0805-FW- R160ELF]	160 Ohm [4114R-1- 161LF]	160 Ohm [CR0402- FX-1600GLF]	160 pF [C0805C161K5GACT U]
160 mOhm [CRL0805-JW- R160ELF]	160 Ohm [4306R- 101-161]	160 Ohm [CR0603- FX-1600ELF]	160 pF [C1206C161KBGAC TU]
160 mOhm [CRL1206-FW- R160ELF]	160 Ohm [4308R- 101-161]	160 Ohm [CR0805- FX-1600ELF]	160 pF [C1210C161KBGAC TU]
160 mOhm [CRL1206-JW- R160ELF]	160 Ohm [4310R- 101-161]	160 Ohm [CR0805- JW-161ELF]	160 pF [C1812C161KBGAC TU]
160 mOhm [CRL2010-FW- R160ELF]	160 Ohm [4310R- 101-161LF]	160 Ohm [CR1206- FX-1600ELF]	160 pF [C1825C161KBGAC TU]
160 mOhm [CRL2010-JW- R160ELF]	160 Ohm [4814P-2- 161]	160 Ohm [CR1206- JW-161ELF]	160 pF [C2220C161KBGAC TU]
160 mOhm [CRL2512-FW- R160ELF]	160 Ohm [4820P-1- 161]	160 Ohm [CRM1206-JW- 161ELF]	160 pF [C2225C161KBGAC TU]
	160 Ohm [CAT16- 161J4LF]	160 Ohm [CRT0805-CX- 1600ELF]	

Multisim 14.1 Base Edition Components

162 kOhm [CAT16-1623F4LF]	162 Ohm [CRT0805-BY-1620ELF]	169 kOhm [CR0603-FX-1693ELF]	17.4 kOhm [CR0805-FX-1742ELF]
162 kOhm [CR0402-FX-1623GLF]	162 Ohm [PWR5322W1620FE]	169 kOhm [CR0805-FX-1693ELF]	17.4 kOhm [CR1206-FX-1742ELF]
162 kOhm [CR0603-FX-1623ELF]	1-640455-0	169 kOhm [CR1206-FX-1693ELF]	17.4 kOhm [CRT0603-CW-1742ELF]
162 kOhm [CR0805-FX-1623ELF]	165 kOhm [CR0402-FX-1653GLF]	169 kOhm [CRT0805-BY-1693ELF]	17.4 Ohm [CR0201-FW-17R4GLF]
162 kOhm [CR1206-FX-1623ELF]	165 kOhm [CR0603-FX-1653ELF]	169 Ohm [CAT16-1690F4LF]	17.4 Ohm [CR0402-FX-17R4GLF]
162 kOhm [CRT0603-BY-1623ELF]	165 kOhm [CR0805-FX-1653ELF]	169 Ohm [CR0402-FX-1690GLF]	17.4 Ohm [CR0603-FX-17R4ELF]
162 kOhm [CRT0805-BY-1623ELF]	165 kOhm [CR1206-FX-1653ELF]	169 Ohm [CR0603-FX-1690ELF]	17.4 Ohm [CR0805-FX-17R4ELF]
162 Ohm [CAT16-1620F4LF]	165 Ohm [CAT16-1650F4LF]	169 Ohm [CR1206-FX-1690ELF]	17.8 kOhm [CR0402-FX-1782GLF]
162 Ohm [CR0402-FX-1620GLF]	165 Ohm [CR0402-FX-1650GLF]	17 mOhm [CRA2512-JZ-R017ELF]	17.8 kOhm [CR0603-FX-1782ELF]
162 Ohm [CR0603-FX-1620ELF]	165 Ohm [CR0603-FX-1650ELF]	17.4 kOhm [CR0402-FX-1742GLF]	17.8 kOhm [CR0805-FX-1782ELF]
162 Ohm [CR0805-FX-1620ELF]	165 Ohm [CR0805-FX-1650ELF]	17.4 kOhm [CR0603-FX-1742ELF]	17.8 kOhm [CR1206-FX-1782ELF]
162 Ohm [CR1206-FX-1620ELF]	169 kOhm [CR0402-FX-1693GLF]		

Multisim 14.1 Base Edition Components

17.8 kOhm [CRT0402-FZ- 1782GLF]	171-025-113R001	174 kOhm [CR1206-FX- 1743ELF]	178 kOhm [CR0603-FX- 1783ELF]
17.8 kOhm [CRT0603-BX- 1782ELF]	171-025-213R001	174 Ohm [CR0201- FW-1740GLF]	178 kOhm [CR0603-FX- 1783GLF]
17.8 kOhm [CRT0603-BY- 1782ELF]	171-037-113R001	174 Ohm [CR0402- FX-1740GLF]	178 kOhm [CR0805-FX- 1783ELF]
17.8 Ohm [CR0402- FX-17R8GLF]	171-037-213R001	174 Ohm [CR0603- FX-1740ELF]	178 kOhm [CR1206-FX- 1783ELF]
17.8 Ohm [CR0603- FX-17R8ELF]	171-050-113R001	174 Ohm [CR0805- FX-1740ELF]	178 kOhm [CR2512-FX- 1783ELF]
17.8 Ohm [CR0805- FX-17R8ELF]	171-050-213R001	174 Ohm [CR1206- FX-1740ELF]	178 kOhm [CRT0805-BY- 1783ELF]
17.8 Ohm [CR1206- FX-17R8ELF]	1734035-1	174 Ohm [CRT0402-BY- 1740GLF]	178 kOhm [CRT1206-DX- 1783ELF]
17.8 Ohm [CRT0402-FZ- 17R8GLF]	173-E09-113R001	174-E09-113R001	178 Ohm [CR0402- FX-1780GLF]
1708026	173-E09-213R001	174-E09-213R001	178 Ohm [CR0603- FX-1780ELF]
1708039	173-E15-113R001	174-E15-113R001	178 Ohm [CR0805- FX-1780ELF]
1708042	173-E15-213R001	174-E15-213R001	178 Ohm [CR0805- FX-1780GLF]
1708055	173-E25-113R001	174-E25-113R001	178 Ohm [CR1206- FX-1780ELF]
1708084	173-E25-213R001	174-E25-213R001	
1708110	174 kOhm [CR0402-FX- 1743GLF]	174-E37-113R001	
171-009-113R001	174 kOhm [CR0603-FX- 1743ELF]	174-E37-213R001	
171-009-213R001	174 kOhm [CR0805-FX- 1743ELF]	174-E50-113R001	
171-015-113R001		174-E50-213R001	
171-015-213R001		178 kOhm [CR0402-FX- 1783GLF]	

Multisim 14.1 Base Edition Components

178 Ohm [CRT0402-FZ- 1780GLF]	18 kOhm [4116R-2- 183LF]	18 kOhm [4310R- 101-183]	18 kOhm [4814P-2- 183LF]
178 Ohm [CRT0805-DZ- 1780ELF]	18 kOhm [4306R- 101-183]	18 kOhm [4310R- 101-183LF]	18 kOhm [4816P-1- 183]
1786837	18 kOhm [4306R- 101-183LF]	18 kOhm [4310R- 102-183]	18 kOhm [4816P-1- 183LF]
1786866	18 kOhm [4306R- 102-183]	18 kOhm [4310R- 102-183LF]	18 kOhm [4816P-2- 183]
1786918	18 kOhm [4306R- 102-183LF]	18 kOhm [4416P-1- 183]	18 kOhm [4816P-2- 183LF]
1786963	18 kOhm [4308H- 101-183]	18 kOhm [4605X- 101-183LF]	18 kOhm [4816P- T01-183]
1787205	18 kOhm [4308H- 102-183]	18 kOhm [4606X- 101-183LF]	18 kOhm [4816P- T01-183LF]
1787234	18 kOhm [4308H- 102-183]	18 kOhm [4606X- 102-183LF]	18 kOhm [4816P- T02-183]
1787289	18 kOhm [4308M- 102-183]	18 kOhm [4608M- 102-183LF]	18 kOhm [4816P- T02-183LF]
18 kOhm [4114R-1- 183]	18 kOhm [4308R- 101-183]	18 kOhm [4608X- 101-183LF]	18 kOhm [4820P-2- 183]
18 kOhm [4114R-1- 183LF]	18 kOhm [4308R- 101-183LF]	18 kOhm [4608X- 102-183LF]	18 kOhm [4820P- T01-183]
18 kOhm [4114R-2- 183]	18 kOhm [4308R- 102-183]	18 kOhm [4609X- 101-183LF]	18 kOhm [4820P- T02-183]
18 kOhm [4116R-1- 183]	18 kOhm [4308R- 102-183LF]	18 kOhm [4610X- 101-183LF]	18 kOhm [CAT16- 1802F4LF]
18 kOhm [4116R-1- 183LF]	18 kOhm [4310M- 101-183]	18 kOhm [4610X- 102-183LF]	18 kOhm [CAT16- 183J4LF]
18 kOhm [4116R-2- 183]	18 kOhm [4310M- 101-183LF]	18 kOhm [4814P-2- 183]	18 kOhm [CAT25- 183JALF]

Multisim 14.1 Base Edition Components

18 kOhm [CAY16-1802F4LF]	18 kOhm [CR2512-JW-183ELF]	18 nF [C0402C183K8RACTU]	18 nF [C0805C183K4RACTU]
18 kOhm [CAY16-183J4LF]	18 kOhm [CRM1206-JW-183ELF]	18 nF [C0402C183K9PACTU]	18 nF [C0805C183K5HACTU]
18 kOhm [CAY16-183J8LF]	18 kOhm [CRT0603-DY-1802ELF]	18 nF [C0402C183K9RACTU]	18 nF [C0805C183K5RACTU]
18 kOhm [CAY17-183JALF]	18 kOhm [CRT0805-BY-1802ELF]	18 nF [C0603C183K1RACTU]	18 nF [C0805C183K8RACTU]
18 kOhm [CR0402-FX-1802GLF]	18 kOhm [CRT1206-BY-1802ELF]	18 nF [C0603C183K3RACTU]	18 nF [C0805C183KARACTU]
18 kOhm [CR0402-JW-183GLF]	18 kOhm [PWR163S-25-1802FE]	18 nF [C0603C183K4RACTU]	18 nF [C0805F183K1RACTU]
18 kOhm [CR0603-FX-1802ELF]	18 kOhm [PWR263S-35-1802JE]	18 nF [C0603C183K5RACTU]	18 nF [C0805F183K3RACTU]
18 kOhm [CR0603-JW-183GLF]	18 MOhm [CHV0805-JW-186ELF]	18 nF [C0603C183K8RACTU]	18 nF [C0805F183K4RACTU]
18 kOhm [CR0805-FX-1802ELF]	18 mOhm [CRF2512-FZ-R018ELF]	18 nF [C0805C183K1RACTU]	18 nF [C0805F183K5RACTU]
18 kOhm [CR0805-JW-183ELF]	18 nF [C0402C183K4RACTU]	18 nF [C0805C183K3GACTU]	18 nF [C1206C183K1HACTU]
18 kOhm [CR1206-FX-1802ELF]	18 nF [C0402C183K8PACTU]	18 nF [C0805C183K3HACTU]	18 nF [C1206C183K1RACTU]
18 kOhm [CR1206-JW-183ELF]			
18 kOhm [CR2010-JW-183ELF]			

Multisim 14.1 Base Edition Components

18 nF [C1206C183K2RACT U]	18 nF [C1210C183KARACT U]	18 nF [GMC7.3182K250K3 1TR12]	18 Ohm [CAT25- 180JALF]
18 nF [C1206C183K3GACT U]	18 nF [C1812C183K1GACT U]	18 nF [GMC7.3182K63K31 TR12]	18 Ohm [CAY10- 180J2LF]
18 nF [C1206C183K3HACT U]	18 nF [C1812C183K1HACT U]	18 nF [GMC7.3183K63K31 TR12]	18 Ohm [CAY10- 180J4LF]
18 nF [C1206C183K5HACT U]	18 nF [C1812C183K5GACT U]	18 nF [MMC5.7183K250J 35TR12]	18 Ohm [CAY16- 180J4LF]
18 nF [C1206C183K5RACT U]	18 nF [C1812C183K5HACT U]	18 nF [MMC7.3183K250K 33TR12]	18 Ohm [CAY16- 180J8LF]
18 nF [C1210C183K1GACT U]	18 nF [C2220C183K2GACT U]	18 Ohm [4116R-1- 180]	18 Ohm [CR0402- FX-18R0GLF]
18 nF [C1210C183K1HACT U]	18 nF [CA064C183K3RAC]	18 Ohm [4608X- 102-180LF]	18 Ohm [CR0402- JW-180GLF]
18 nF [C1210C183K3HACT U]	18 nF [CDR03BX183BKSM]	18 Ohm [4816P-1- 180]	18 Ohm [CR0603- FX-18R0ELF]
18 nF [C1210C183K5GACT U]	18 nF [GMC5.7182K250J3 1TR12]	18 Ohm [4816P-1- 180LF]	18 Ohm [CR0603- JW-180ELF]
18 nF [C1210C183K5HACT U]	18 nF [GMC5.7183K100J3 1TR12]	18 Ohm [4816P- T01-180]	18 Ohm [CR0603- JW-180GLF]
18 nF [C1210C183K5RACT U]	18 nF [GMC5.7183K50J31 TR12]	18 Ohm [CAT10- 180J4LF]	18 Ohm [CR0805- FX-18R0ELF]
		18 Ohm [CAT16- 180J4LF]	18 Ohm [CR0805- JW-180ELF]
		18 Ohm [CAT16- 180J8LF]	18 Ohm [CR1206- FX-18R0ELF]

Multisim 14.1 Base Edition Components

18 Ohm [CR1206-JW-180ELF]	18 pF [C0603C180K3GACT U]	18 pF [C1210C180KBGAC TU]	18 uH [SDE1006A-180M]
18 Ohm [CR1206-JW-180GLF]	18 pF [C0603C180K5GACT U]	18 pF [C1812C180KBGAC TU]	18 uH [SDR0302-180ML]
18 Ohm [CR2010-JW-180ELF]	18 pF [C0603C180K8GACT U]	18 pF [C1825C180KBGAC TU]	18 uH [SDR0403-180ML]
18 Ohm [CR2512-JW-180ELF]	18 pF [C0805C180K1GACT U]	18 pF [C2220C180KBGAC TU]	18 uH [SDR0503-180ML]
18 Ohm [CRM1206-FX-18R0ELF]	18 pF [C0805C180K2GACT U]	18 pF [C2225C180KBGAC TU]	18 uH [SDR0603-180ML]
18 Ohm [CRT0805-BW-18R0ELF]	18 pF [C0805C180K3GACT U]	18 uF [C1210C186K4PACT U]	18 uH [SDR0604-180YL]
18 Ohm [CRT1206-CW-18R0ELF]	18 pF [C0805C180K5GACT U]	18 uF [C1210C186K8PACT U]	18 uH [SDR0703-180KL]
18 Ohm [FW20A18R0JA]	18 pF [C0805C180KBGAC TU]	18 uF [C1210C186K9PACT U]	18 uH [SDR0805-180ML]
18 pF [C0201C180K3GACT U]	18 pF [C1206C180K1GACT U]	18 uH [SDE0403A-180M]	18 uH [SDR0906-180ML]
18 pF [C0402C180K3GACT U]	18 pF [C1206C180K5GACT U]	18 uH [SDE0604A-180M]	18 uH [SDR1006-180ML]
18 pF [C0402C180K5GACT U]	18 pF [C1206C180K8GACT U]	18 uH [SDE0805A-180M]	18 uH [SDR1105-180ML]
18 pF [C0603C180K2GACT U]			18 uH [SDR1307-180ML]
			18 uH [SDR1307A-180M]
			18 uH [SRN1060-180M]
			18 uH [SRN3015-180M]

Multisim 14.1 Base Edition Components

18 uH [SRR0735A-180M]	18 uH [SRR1260-180M]	18.2 kOhm [CR0805-FX-1822ELF]	18.7 kOhm [CR0805-FX-1872ELF]
18 uH [SRR0745A-180M]	18 uH [SRR1260A-180M]	18.2 kOhm [CR1206-FX-1822ELF]	18.7 kOhm [CR1206-FX-1872ELF]
18 uH [SRR0804-180Y]	18 uH [SRR1280-180M]	18.2 kOhm [CRT0603-BY-1822ELF]	18.7 Ohm [CR0603-FX-18R7ELF]
18 uH [SRR0805-180Y]	18 uH [SRR4018-180Y]	18.2 kOhm [CRT0805-BY-1822ELF]	18.7 Ohm [CR1206-FX-18R7ELF]
18 uH [SRR0905-180M]	18 uH [SRR4028-180Y]	18.2 kOhm [CRT0805-PW-1822ELF]	180 kOhm [4114R-1-184]
18 uH [SRR0906-180ML]	18 uH [SRR5018-180Y]	18.2 Ohm [CR0402-FX-18R2GLF]	180 kOhm [4114R-1-184LF]
18 uH [SRR0908-180ML]	18 uH [SRR5028-180Y]	18.2 Ohm [CR0603-FX-18R2ELF]	180 kOhm [4116R-1-184]
18 uH [SRR1003-180M]	18 uH [SRR6028-180Y]	18.2 Ohm [CR0603-FX-18R2GLF]	180 kOhm [4116R-1-184LF]
18 uH [SRR1005-180Y]	18 uH [SRR6038-180Y]	18.2 Ohm [CR0805-FX-18R2ELF]	180 kOhm [4116R-2-184LF]
18 uH [SRR1205-180ML]	18 uH [SRR6040A-180M]	18.2 Ohm [CR1206-FX-18R2ELF]	180 kOhm [4306R-101-184]
18 uH [SRR1206-180ML]	18 uH [SRR7045-180M]	18.7 kOhm [CR0402-FX-1872GLF]	180 kOhm [4306R-101-184LF]
18 uH [SRR1208-180ML]	18 uH [SRU8043-180Y]	18.7 kOhm [CR0603-FX-1872ELF]	180 kOhm [4306R-102-184]
18 uH [SRR1210-180M]	18.2 kOhm [CR0402-FX-1822GLF]		180 kOhm [4306R-101-184LF]
18 uH [SRR1210A-180M]	18.2 kOhm [CR0603-FX-1822ELF]		180 kOhm [4308R-101-184]
18 uH [SRR1240-180M]			

Multisim 14.1 Base Edition Components

180 kOhm [4308R-101-184LF]	180 kOhm [4610X-101-184LF]	180 kOhm [CR0402-FX-1803GLF]	180 kOhm [CRT1206-DY-1803ELF]
180 kOhm [4308R-102-184]	180 kOhm [4610X-102-184LF]	180 kOhm [CR0402-JW-184GLF]	180 mOhm [CRL0603-FW-R180ELF]
180 kOhm [4308R-102-184LF]	180 kOhm [4816P-1-184]	180 kOhm [CR0603-FX-1803ELF]	180 mOhm [CRL0603-JW-R180ELF]
180 kOhm [4310M-101-184]	180 kOhm [4816P-1-184LF]	180 kOhm [CR0603-JW-184ELF]	180 mOhm [CRL0805-FW-R180ELF]
180 kOhm [4310R-101-184]	180 kOhm [4816P-2-184]	180 kOhm [CR0805-FX-1803ELF]	180 mOhm [CRL1206-FW-R180ELF]
180 kOhm [4310R-101-184LF]	180 kOhm [4816P-2-184LF]	180 kOhm [CR1206-FX-1803ELF]	180 mOhm [CRL1206-JW-R180ELF]
180 kOhm [4310R-102-184]	180 kOhm [4816P-T01-184]	180 kOhm [CR1206-JW-184ELF]	180 mOhm [CRL2010-FW-R180ELF]
180 kOhm [4416P-1-184]	180 kOhm [4816P-T01-184LF]	180 kOhm [CR2010-JW-184ELF]	180 nF [C0603C184K4RACT U]
180 kOhm [4605X-101-184LF]	180 kOhm [4816P-T02-184]	180 kOhm [CRM1206-JW-184ELF]	180 nF [C0603C184K8RACT U]
180 kOhm [4606X-101-184LF]	180 kOhm [4816P-T02-184LF]		
180 kOhm [4606X-102-184LF]	180 kOhm [CAT16-184J4LF]		
180 kOhm [4608X-101-184LF]	180 kOhm [CAT25-184JALF]		
180 kOhm [4608X-102-184LF]	180 kOhm [CAY16-1803F4LF]		
180 kOhm [4609X-101-184LF]	180 kOhm [CAY16-184J4LF]		
180 kOhm [4610H-102-184LF]	180 kOhm [CAY16-184J8LF]		

Multisim 14.1 Base Edition Components

180 nF [C0805C184K3RACT U]	180 nF [C1210C184K1RACT U]	180 nF [C1812F184K2RACT U]	180 nF [MDC10184K630A5 8P7TUBE]
180 nF [C0805C184K4RACT U]	180 nF [C1210C184K3HACT U]	180 nF [C1812F184K3RACT U]	180 nF [MDC10184K630A5 8P8TUBE]
180 nF [C0805C184K5RACT U]	180 nF [C1210C184K5RACT U]	180 nF [C1812F184K5RACT U]	180 nF [MDC15184K100B5 3P3TUBE]
180 nF [C0805C184K8RACT U]	180 nF [C1210F184K1RACT U]	180 nF [C1825C184K5RACT U]	180 nF [MDC15184K250B5 3P3TUBE]
180 nF [C1206C184K1RACT U]	180 nF [C1210F184K3RACT U]	180 nF [C2225C184K1RACT U]	180 nF [MDC15184K400B5 3P3TUBE]
180 nF [C1206C184K5RACT U]	180 nF [C1210F184K4RACT U]	180 nF [GMC5.7184K50J35 TR12]	180 nF [MDC15184K50B53 P3TUBE]
180 nF [C1206C184M5UAC TU]	180 nF [C1210F184K5RACT U]	180 nF [GMC7.3184K63K33 TR12]	180 nF [MDK15184K50B53 P3TUBE]
180 nF [C1206F184K1RACT U]	180 nF [C1812C184K1RACT U]	180 nF [MDC10184K100A5 2P3TUBE]	180 nF [MDS15184K400B5 3P3TUBE]
180 nF [C1206F184K3RACT U]	180 nF [C1812C184K5HACT U]	180 nF [MDC10184K250A5 2P3TUBE]	180 nF [MDS15184K50B53 P3TUBE]
180 nF [C1206F184K4RACT U]	180 nF [C1812C184K5RACT U]	180 nF [MDC10184K400A5 2P3TUBE]	180 nF [MMC7.3184K50K3 3TR12]
180 nF [C1206F184K5RACT U]	180 nF [C1812F184K1RACT U]	180 nF [MDC10184K50A52 P3TUBE]	180 Ohm [4114R-1- 181] 180 Ohm [4114R-1- 181LF]

Multisim 14.1 Base Edition Components

180 Ohm [4114R-2-181]	180 Ohm [4308R-101-181]	180 Ohm [4420P-T01-181]	180 Ohm [4612X-102-181LF]
180 Ohm [4114R-2-181LF]	180 Ohm [4308R-101-181LF]	180 Ohm [4604X-102-181LF]	180 Ohm [4814P-1-181]
180 Ohm [4116R-1-181]	180 Ohm [4308R-102-181]	180 Ohm [4605X-101-181LF]	180 Ohm [4814P-2-181]
180 Ohm [4116R-1-181LF]	180 Ohm [4308R-102-181LF]	180 Ohm [4606X-101-181LF]	180 Ohm [4814P-2-181LF]
180 Ohm [4116R-2-181]	180 Ohm [4309R-101-181]	180 Ohm [4606X-102-181LF]	180 Ohm [4814P-T01-181]
180 Ohm [4116R-2-181LF]	180 Ohm [4310M-101-181]	180 Ohm [4607X-101-181LF]	180 Ohm [4814P-T01-181LF]
180 Ohm [4306H-101-181]	180 Ohm [4310M-101-181LF]	180 Ohm [4608X-101-181LF]	180 Ohm [4814P-T02-181]
180 Ohm [4306H-101-181LF]	180 Ohm [4310R-101-181]	180 Ohm [4608X-102-181LF]	180 Ohm [4816P-1-181]
180 Ohm [4306R-101-181]	180 Ohm [4310R-101-181LF]	180 Ohm [4608X-AP1-181LF]	180 Ohm [4816P-1-181LF]
180 Ohm [4306R-101-181LF]	180 Ohm [4310R-102-181]	180 Ohm [4609X-101-181LF]	180 Ohm [4816P-2-181]
180 Ohm [4306R-102-181]	180 Ohm [4310R-102-181LF]	180 Ohm [4610H-101-181LF]	180 Ohm [4816P-2-181LF]
180 Ohm [4306R-102-181LF]	180 Ohm [4416P-1-181]	180 Ohm [4610M-101-181LF]	180 Ohm [4816P-T01-181]
180 Ohm [4308H-101-181]	180 Ohm [4416P-2-181]	180 Ohm [4610X-101-181LF]	180 Ohm [4816P-T01-181LF]
180 Ohm [4308M-101-181]	180 Ohm [4416P-T01-181]	180 Ohm [4610X-102-181LF]	180 Ohm [4816P-T02-181]
180 Ohm [4308M-101-181LF]	180 Ohm [4420P-1-181]	180 Ohm [4610X-AP1-181LF]	180 Ohm [4816P-T02-181LF]

Multisim 14.1 Base Edition Components

180 Ohm [4820P-1-181]	180 Ohm [CR0805-FX-1800GLF]	180 Ohm [PWR6327W1800JE]	180 pF [C0603C181K4RACTU]
180 Ohm [CAT10-181J4LF]	180 Ohm [CR0805-JW-181ELF]	180 pF [C0402C181K1HACTU]	180 pF [C0603C181K5GACTU]
180 Ohm [CAT16-1800F4LF]	180 Ohm [CR0805-JW-181GLF]	180 pF [C0402C181K3HACTU]	180 pF [C0603C181K5RACTU]
180 Ohm [CAT16-181J4LF]	180 Ohm [CR1206-FX-1800ELF]	180 pF [C0402C181K3RACTU]	180 pF [C0603C181K8RACTU]
180 Ohm [CAT16-181J8LF]	180 Ohm [CR2010-JW-181ELF]	180 pF [C0402C181K4RACTU]	180 pF [C0805C181K1GACTU]
180 Ohm [CAT25-181JALF]	180 Ohm [CR2512-FX-1800ELF]	180 pF [C0402C181K5HACTU]	180 pF [C0805C181K2GACTU]
180 Ohm [CAY10-181J4LF]	180 Ohm [CR2512-JW-181ELF]	180 pF [C0402C181K5RACTU]	180 pF [C0805C181K5GACTU]
180 Ohm [CAY16-181J4LF]	180 Ohm [CRT0805-FV-1800ELF]	180 pF [C0402C181K8RACTU]	180 pF [C1206C181K1GACTU]
180 Ohm [CAY16-181J8LF]	180 Ohm [PWR2010W1800JE]	180 pF [C0603C181K1RACTU]	180 pF [C1206C181K2GACTU]
180 Ohm [CR0402-FX-1800GLF]	180 Ohm [PWR263S-35-1800J]	180 pF [C0603C181K2RACTU]	180 pF [C1206C181KBGACTU]
180 Ohm [CR0402-JW-181GLF]	180 Ohm [PWR4525W1800J]	180 pF [C0603C181K3RACTU]	
180 Ohm [CR0603-FX-1800ELF]	180 Ohm [PWR5322W1800JE]		
180 Ohm [CR0603-JW-181ELF]			
180 Ohm [CR0603-JW-181GLF]			
180 Ohm [CR0805-FX-1800ELF]			

Multisim 14.1 Base Edition Components

180 pF [C1210C181KBGAC TU]	180 uF [A700D187M002AT E015]	180 uF [EEFCX0J181R]	180 uH [SDR0503- 181KL]
180 pF [C1812C181KBGAC TU]	180 uF [A700D187M002AT E018]	180 uF [EEFLR0E181R]	180 uH [SDR0603- 181KL]
180 pF [C1825C181KBGAC TU]	180 uF [A700D187M004AT E015]	180 uF [EEFLS0E181R]	180 uH [SDR0703- 181KL]
180 pF [C2220C181KBGAC TU]	180 uF [A700D187M004AT E018]	180 uF [EEFSR0E181R]	180 uH [SDR0805- 181KL]
180 pF [C2225C181KBGAC TU]	180 uF [A700D187M2R5AT E015]	180 uF [EEFSR0E181R4]	180 uH [SDR0906- 181KL]
180 pF [CA064C181K4GAC TU]	180 uF [A700D187M2R5AT E018]	180 uF [EEFSX0D181ER]	180 uH [SDR1307- 181KL]
180 pF [CA064C181K5GAC TU]	180 uF [A700X187M004AT E010]	180 uF [EEFSX0E181ER]	180 uH [SDR1307A-181K]
180 uF [16SEPF180M]	180 uF [A700X187M006AT E010]	180 uF [EEFSX0G181ER]	180 uH [SRR0735A- 181M]
180 uF [16SVPE180M]	180 uF [A700X187M006AT E015]	180 uF [EEFSX0J181ER]	180 uH [SRR0745A- 181M]
180 uF [16SVPF180M]	180 uF [EEFCT0G181R]	180 uH [SDE0805A- 181K]	180 uH [SRR0804- 181K]
180 uF [2R5SVPC180MY]	180 uF [EEFCX0G181R]	180 uH [SDE1006A- 181K]	180 uH [SRR0805- 181K]
180 uF [6SVPE180M]	180 uF [EEFCX0G181XR]	180 uH [SDR0302- 181KL]	180 uH [SRR0905- 181K]
		180 uH [SDR0403- 181KL]	180 uH [SRR0906- 181YL]

Multisim 14.1 Base Edition Components

180 uH [SRR0908-181YL]	180 uH [SRR7045-181M]	182 Ohm [CR0805-FX-1820ELF]	187 kOhm [CR0402-FX-1873GLF]
180 uH [SRR1003-181M]	181-015-113R431	182 Ohm [CR1206-FX-1820ELF]	187 kOhm [CR0603-FX-1873ELF]
180 uH [SRR1005-181K]	181-015-213R431	182 Ohm [CRT0402-DZ-1820GLF]	187 kOhm [CR0603-FX-1873GLF]
180 uH [SRR1205-181KL]	181-026-113R431	182 Ohm [CRT0603-BY-1820ELF]	187 kOhm [CR0805-FX-1873ELF]
180 uH [SRR1206-181KL]	181-026-213R431	182-009-113R431	187 kOhm [CR1206-FX-1873ELF]
180 uH [SRR1208-181YL]	181-044-113R431	182-009-213R431	187 kOhm [CR1206-FX-1873ELF]
180 uH [SRR1210-181M]	181-044-213R431	182-015-113R431	187 kOhm [CRT0805-BY-1873ELF]
180 uH [SRR1210A-181M]	181-062-113R431	182-015-213R431	187 Ohm [CR0402-FX-1870GLF]
180 uH [SRR1240-181K]	181-062-213R431	182-025-113R431	187 Ohm [CR0603-FX-1870ELF]
180 uH [SRR1260-181K]	181-078-113R431	182-025-213R431	187 Ohm [CR0805-FX-1870ELF]
180 uH [SRR1260A-181K]	181-078-213R431	182-037-113R431	187 Ohm [CR1206-FX-1870ELF]
180 uH [SRR1280-181K]	182 kOhm [CR0402-FX-1823GLF]	182-037-213R431	187 Ohm [CRT1206-FZ-1870ELF]
180 uH [SRR4018-181Y]	182 kOhm [CR0603-FX-1823ELF]	183-009-113R161	19 kOhm [PWR263S-35-1902J]
180 uH [SRR4028-181Y]	182 kOhm [CR0805-FX-1823ELF]	183-009-213R161	
180 uH [SRR5018-181Y]	182 kOhm [CR1206-FX-1823ELF]	183-015-113R161	
	182 Ohm [CAY16-1820F4LF]	183-015-213R161	
	182 Ohm [CR0402-FX-1820GLF]	183-025-113R161	
	182 Ohm [CR0603-FX-1820ELF]	183-025-213R161	

Multisim 14.1 Base Edition Components

19 kOhm [PWR263S-35- 1902JE]	19.6 kOhm [CR0805-FX- 1962ELF]	191 kOhm [CRT0805-BY- 1913ELF]	1981584-1 1B4B42
19.1 kOhm [CAT16- 1912F4LF]	19.6 kOhm [CR1206-FX- 1962ELF]	191 Ohm [CR0201- FW-1910GLF]	1BH62 1DH62
19.1 kOhm [CR0201-FW- 1912GLF]	19.6 kOhm [CRT0402-FZ- 1962GLF]	191 Ohm [CR0402- FX-1910GLF]	1G4B42 1GH62
19.1 kOhm [CR0402-FX- 1912GLF]	19.6 kOhm [CRT0805-BY- 1962ELF]	191 Ohm [CR0603- FX-1910ELF]	1J4B42 1JH62
19.1 kOhm [CR0603-FX- 1912ELF]	19.6 Ohm [CR0805- FX-19R6ELF]	191 Ohm [CR1206- FX-1910ELF]	1LH62 1N1199C
19.1 kOhm [CR0805-FX- 1912ELF]	19.6 Ohm [CR1206- FX-19R6ELF]	1932258-1	1N1200C 1N1202C
19.1 kOhm [CR1206-FX- 1912ELF]	19.6 Ohm [CRT0402-FZ- 19R6GLF]	196 kOhm [CR0603-FX- 1963ELF]	1N1204C 1N1206C
19.1 kOhm [CRT0603-BY- 1912ELF]	191 kOhm [CR0402-FX- 1913GLF]	196 kOhm [CR0805-FX- 1963ELF]	1N3064 1N3208
19.1 Ohm [CR0805- FX-19R1ELF]	191 kOhm [CR0603-FX- 1913ELF]	196 Ohm [CR0603- FX-1960ELF]	1N3491 1N3492
19.1 Ohm [CR1206- FX-19R1ELF]	191 kOhm [CR0805-FX- 1913ELF]	196 Ohm [CR0805- FX-1960ELF]	1N3493 1N3494
19.6 kOhm [CR0402-FX- 1962GLF]	191 kOhm [CR1206-FX- 1913ELF]	196 Ohm [CR1206- FX-1960ELF]	1N3495 1N3611GP
19.6 kOhm [CR0603-FX- 1962ELF]	191 kOhm [CRT0402-BY- 1913GLF]	196 Ohm [CRT0402-FZ- 1960GLF]	1N3612GP 1N3613GP
			1N3614GP

Multisim 14.1 Base Edition Components

1N3659	1N3899	1N4005RLG	1N4371A
1N3660	1N3900	1N4006FFG	1N4372A
1N3661	1N3901	1N4006G	1N4383GP
1N3662	1N3902	1N4006GP	1N4384GP
1N3663	1N3903	1N4006RLG	1N4385GP
1N3879	1N3909	1N4007-E3/54	1N4446
1N3879A	1N3910	1N4007FFG	1N4447
1N3880	1N3911	1N4007G	1N4448
1N3880A	1N3912	1N4007GP	1N4449
1N3881	1N3913	1N4007RLG	1N4454
1N3881A	1N3957GP	1N4009	1N4585GP
1N3882	1N4001G	1N4148	1N4586GP
1N3882A	1N4001GP	1N4149	1N4678
1N3883	1N4001RLG	1N4150	1N4681
1N3883A	1N4002G	1N4151	1N4728A
1N3889	1N4002GP	1N4152	1N4729A
1N3889A	1N4002RLG	1N4153	1N4730A
1N3890	1N4003G	1N4154	1N4731A
1N3890A	1N4003GP	1N4245GP	1N4732A
1N3891	1N4003RLG	1N4246GP	1N4733A
1N3891A	1N4004G	1N4247GP	1N4734A
1N3892	1N4004GP	1N4248GP	1N4735A
1N3892A	1N4004RLG	1N4249GP	1N4736A
1N3893	1N4005G	1N4305	1N4737A
1N3893A	1N4005GP	1N4370A	1N4738A

Multisim 14.1 Base Edition Components

1N4739A	1N4764A	1N5062GP	1N5245B
1N4740A	1N4933	1N5221B	1N5246B
1N4741A	1N4933G	1N5222B	1N5247B
1N4742A	1N4933RLG	1N5223B	1N5248B
1N4743A	1N4934	1N5224B	1N5249B
1N4744A	1N4934G	1N5225B	1N5250B
1N4745A	1N4934RLG	1N5226B	1N5251B
1N4746A	1N4935	1N5227B	1N5252B
1N4747A	1N4935G	1N5228B	1N5253B
1N4748A	1N4935RLG	1N5229B	1N5254B
1N4749A	1N4936	1N5230B	1N5255B
1N4750A	1N4936G	1N5231B	1N5256B
1N4751A	1N4936RLG	1N5232B	1N5257B
1N4752A	1N4937	1N5233B	1N5258B
1N4753A	1N4937G	1N5234B	1N5259B
1N4754A	1N4937RLG	1N5235B	1N5260B
1N4755A	1N4938	1N5236B	1N5261B
1N4756A	1N4942GP	1N5237B	1N5262B
1N4757A	1N4944GP	1N5238B	1N5263B
1N4758A	1N4946GP	1N5239B	1N5264B
1N4759A	1N4947GP	1N5240B	1N5265B
1N4760A	1N4948GP	1N5241B	1N5266B
1N4761A	1N5059GP	1N5242B	1N5267B
1N4762A	1N5060GP	1N5243B	1N5268B
1N4763A	1N5061GP	1N5244B	1N5269B

Multisim 14.1 Base Edition Components

1N5270B	1N5340BRLG	1N5353BRLG	1N5368BRLG
1N5271B	1N5341BG	1N5355BG	1N5369BG
1N5272B	1N5341BRLG	1N5355BRLG	1N5369BRLG
1N5273B	1N5342BG	1N5356BRLG	1N5371BRLG
1N5274B	1N5342BRLG	1N5357BG	1N5372BG
1N5275B	1N5343BG	1N5357BRLG	1N5372BRLG
1N5276B	1N5343BRLG	1N5358BG	1N5373BG
1N5277B	1N5344BG	1N5358BRLG	1N5373BRLG
1N5278B	1N5344BRLG	1N5359BG	1N5374BG
1N5279B	1N5345BRLG	1N5359BRLG	1N5374BRLG
1N5280B	1N5346BG	1N5361BG	1N5375BG
1N5281B	1N5346BRLG	1N5361BRLG	1N5375BRLG
1N5333BRLG	1N5347BG	1N5362BG	1N5378BG
1N5334BRLG	1N5347BRLG	1N5362BRLG	1N5378BRLG
1N5335BG	1N5348BG	1N5363BG	1N5381BRLG
1N5335BRLG	1N5348BRLG	1N5363BRLG	1N5383BG
1N5336BG	1N5349BG	1N5364BG	1N5383BRLG
1N5336BRLG	1N5349BRLG	1N5364BRLG	1N5384BG
1N5337BG	1N5350BG	1N5365BG	1N5384BRLG
1N5337BRLG	1N5350BRLG	1N5365BRLG	1N5386BG
1N5338BG	1N5351BG	1N5366BG	1N5386BRLG
1N5338BRLG	1N5351BRLG	1N5366BRLG	1N5388BG
1N5339BG	1N5352BG	1N5367BG	1N5388BRLG
1N5339BRLG	1N5352BRLG	1N5367BRLG	1N5391
1N5340BG	1N5353BG	1N5368BG	1N5391GP

Multisim 14.1 Base Edition Components

1N5392GP	1N5408-E3/54	1N5821	1N5918B
1N5393GP	1N5408G	1N5821G	1N5919B
1N5394GP	1N5408RLG	1N5821RLG	1N5919BG
1N5395GP	1N5615GP	1N5822	1N5919BRLG
1N5396GP	1N5617GP	1N5822-E3/54	1N5920B
1N5397GP	1N5619GP	1N5822G	1N5920BG
1N5398GP	1N5621GP	1N5822RLG	1N5921B
1N5399GP	1N5623GP	1N5823	1N5921BG
1N5400	1N5758	1N5824	1N5921BRLG
1N5400G	1N5758A	1N5825	1N5922B
1N5400RLG	1N5759	1N5826	1N5923B
1N5401	1N5759A	1N5827	1N5923BRLG
1N5401G	1N5760	1N5828	1N5924B
1N5401RLG	1N5761	1N5829	1N5924BRLG
1N5402	1N5761A	1N5830	1N5925B
1N5402G	1N5817-E3/54	1N5831	1N5925BRLG
1N5402RLG	1N5817G	1N5832	1N5926B
1N5404	1N5817RLG	1N5833	1N5927B
1N5404G	1N5818G	1N5834	1N5927BG
1N5404RLG	1N5818RLG	1N5913B	1N5927BRLG
1N5406	1N5819G	1N5913BRLG	1N5928B
1N5406G	1N5819RLG	1N5914B	1N5929B
1N5406RLG	1N5820	1N5915B	1N5929BG
1N5407G	1N5820G	1N5916B	1N5929BRLG
1N5407RLG	1N5820RLG	1N5917B	1N5930B

Multisim 14.1 Base Edition Components

1N5931B	1N5946B	1N6001B	1N6096
1N5931BRLG	1N5946BRLG	1N6002B	1N6098
1N5932B	1N5947B	1N6003B	1N6285AG
1N5932BRLG	1N5948BRLG	1N6004B	1N6285ARL4G
1N5933B	1N5953BG	1N6005B	1N6287AG
1N5934B	1N5953BRLG	1N6006B	1N6287ARL4G
1N5934BG	1N5955BRLG	1N6007B	1N6292AG
1N5934BRLG	1N5956BG	1N6008B	1N6292ARL4G
1N5935B	1N5956BRLG	1N6009B	1N6294ARL4G
1N5935BRLG	1N5985B	1N6010B	1N6373-E3/51
1N5936B	1N5986B	1N6011B	1N6478
1N5937B	1N5987B	1N6012B	1N6479
1N5937BRLG	1N5988B	1N6013B	1N6480
1N5938B	1N5989B	1N6014B	1N6481
1N5938BRLG	1N5990B	1N6015B	1N6482
1N5939B	1N5991B	1N6016B	1N6483
1N5940B	1N5992B	1N6017B	1N6484
1N5940BRLG	1N5993B	1N6018B	1N747A
1N5941B	1N5994B	1N6019B	1N748A
1N5941BRLG	1N5995B	1N6020B	1N749A
1N5942B	1N5996B	1N6021B	1N750A
1N5942BRLG	1N5997B	1N6022B	1N751A
1N5943B	1N5998B	1N6023B	1N752A
1N5944B	1N5999B	1N6024B	1N753A
1N5945B	1N6000B	1N6025B	1N754A

Multisim 14.1 Base Edition Components

1N755A	1N971B	1P3S	1PS74SB23
1N756A	1N972B	1PMT12AT1G	1PS75SB45
1N757A	1N973B	1PMT16AT3G	1PS76SB10
1N758A	1N974B	1PMT33AT3G	1PS76SB17
1N759A	1N975B	1PMT5.0AT1G	1PS76SB40
1N914	1N976B	1PMT5927BT1G	1PS76SB70
1N914A	1N977B	1PS10SB82	1PS79SB10
1N914B	1N978B	1PS300	1PS79SB17
1N916	1N979B	1PS301	1PS79SB30
1N916A	1N980B	1PS302	1PS79SB31
1N916B	1N981B	1PS66SB17	1PS79SB40
1N957B	1N982B	1PS66SB82	1PS79SB70
1N958B	1N983B	1PS70SB10	1PS88SB48
1N959B	1N984B	1PS70SB14	1PS88SB82
1N960B	1N985B	1PS70SB15	1S1553
1N961B	1N986B	1PS70SB16	1S1554
1N962B	1N987B	1PS70SB20	1S1555
1N963B	1N988B	1PS70SB40	1S1830
1N964B	1N989B	1PS70SB44	1S1834
1N965B	1N990B	1PS70SB45	1S1835
1N966B	1N991B	1PS70SB46	1S1885
1N967B	1N992B	1PS70SB82	1S1887
1N968B	1P1S	1PS70SB84	1S1888
1N969B	1P1S_TAPPED	1PS70SB85	1S953
1N970B	1P2S	1PS70SB86	1S954

Multisim 14.1 Base Edition Components

1S955	1SMB28CAT3G	1SMB5940BT3G	1ZB14
1SMA12CAT3G	1SMB30AT3G	1SMB70AT3G	1ZB15
1SMA26AT3G	1SMB30CAT3G	1SMB85AT3G	1ZB30
1SMA30AT3G	1SMB33CAT3G	1SMC28AT3G	1ZB6.8
1SMA40CAT3G	1SMB36CAT3G	1SMC36AT3G	1ZB7.5
1SMA5.0AT3G	1SMB5.0AT3G	1SMC6.0AT3G	1ZB8.2
1SMA5913BT3G	1SMB54CAT3G	1SS400T1G	1ZB9.1
1SMA5918BT3G	1SMB58CAT3G	1SV233-TB-E	2 kOhm [4108R-1-202LF]
1SMA5921BT3G	1SMB5914BT3G	1SV234-TB-E	2 kOhm [4114R-1-202]
1SMA5922BT3G	1SMB5918BT3G	1Z10	2 kOhm [4114R-1-202]
1SMA5927BT3G	1SMB5919BT3G	1Z11	2 kOhm [4114R-1-202LF]
1SMA5931BT3G	1SMB5920BT3G	1Z12	2 kOhm [4114R-2-202]
1SMA5932BT3G	1SMB5921BT3G	1Z13	2 kOhm [4114R-2-202]
1SMA5936BT3G	1SMB5922BT3G	1Z14	2 kOhm [4114R-2-202LF]
1SMA5940BT3G	1SMB5924BT3G	1Z15	2 kOhm [4114R-2-202LF]
1SMB12AT3G	1SMB5925BT3G	1Z30	2 kOhm [4116R-1-202]
1SMB14AT3G	1SMB5927BT3G	1Z6.2	2 kOhm [4116R-1-202LF]
1SMB170AT3G	1SMB5930BT3G	1Z6.8	2 kOhm [4116R-2-202]
1SMB18CAT3G	1SMB5931BT3G	1Z7.5	2 kOhm [4116R-2-202]
1SMB20CAT3G	1SMB5933BT3G	1Z8.2	2 kOhm [4116R-2-202LF]
1SMB22CAT3G	1SMB5934BT3G	1Z9.1	2 kOhm [4304M-101-202]
1SMB24AT3G	1SMB5935BT3G	1ZB10	2 kOhm [4304M-101-202]
1SMB24CAT3G	1SMB5936BT3G	1ZB11	2 kOhm [4304M-101-202LF]
1SMB26CAT3G	1SMB5937BT3G	1ZB12	2 kOhm [4304M-101-202LF]
1SMB28AT3G	1SMB5939BT3G	1ZB13	

Multisim 14.1 Base Edition Components

2 kOhm [4306M-101-202]	2 kOhm [4309R-101-202LF]	2 kOhm [4604X-101-202LF]	2 kOhm [4610H-102-202LF]
2 kOhm [4306M-102-202]	2 kOhm [4310H-101-202]	2 kOhm [4604X-102-202LF]	2 kOhm [4610X-101-202LF]
2 kOhm [4306M-102-202LF]	2 kOhm [4310H-101-202LF]	2 kOhm [4605X-101-202LF]	2 kOhm [4610X-102-202LF]
2 kOhm [4306R-101-202]	2 kOhm [4310M-101-202]	2 kOhm [4606X-101-202LF]	2 kOhm [4610X-AP1-202LF]
2 kOhm [4306R-101-202LF]	2 kOhm [4310M-102-202]	2 kOhm [4606X-102-202LF]	2 kOhm [4611X-101-202LF]
2 kOhm [4306R-102-202]	2 kOhm [4310M-102-202LF]	2 kOhm [4606X-AP2-202LF]	2 kOhm [4612X-101-202LF]
2 kOhm [4306R-102-202LF]	2 kOhm [4310R-101-202]	2 kOhm [4608H-101-202LF]	2 kOhm [4612X-102-202LF]
2 kOhm [4308H-102-202]	2 kOhm [4310R-101-202LF]	2 kOhm [4608H-102-202LF]	2 kOhm [4814P-1-202]
2 kOhm [4308M-102-202]	2 kOhm [4310R-102-202]	2 kOhm [4608X-101-202LF]	2 kOhm [4814P-1-202LF]
2 kOhm [4308M-102-202LF]	2 kOhm [4310R-102-202LF]	2 kOhm [4608X-102-202LF]	2 kOhm [4814P-2-202]
2 kOhm [4308R-101-202]	2 kOhm [4416P-1-202]	2 kOhm [4608X-AP1-202LF]	2 kOhm [4814P-2-202LF]
2 kOhm [4308R-101-202LF]	2 kOhm [4416P-T01-202]	2 kOhm [4608X-AP2-202LF]	2 kOhm [4814P-T01-202]
2 kOhm [4308R-102-202]	2 kOhm [4420P-2-202]	2 kOhm [4609M-101-202LF]	2 kOhm [4814P-T01-202LF]
2 kOhm [4308R-102-202LF]	2 kOhm [4420P-2-202LF]	2 kOhm [4609X-101-202LF]	2 kOhm [4814P-T02-202]
2 kOhm [4309R-101-202]	2 kOhm [4420P-T02-202]	2 kOhm [4610H-101-202LF]	2 kOhm [4814P-T02-202LF]

Multisim 14.1 Base Edition Components

2 kOhm [4816P-1-202]	2 kOhm [CAT10-202J4LF]	2 kOhm [CR0603-FX-2001ELF]	2 kOhm [CRT0603-BY-2001ELF]
2 kOhm [4816P-1-202LF]	2 kOhm [CAT16-2001F4LF]	2 kOhm [CR0603-JW-202ELF]	2 kOhm [CRT0603-DY-2001ELF]
2 kOhm [4816P-2-202]	2 kOhm [CAT16-202J2LF]	2 kOhm [CR0603-JW-202GLF]	2 kOhm [CRT0603-FY-2001ELF]
2 kOhm [4816P-2-202LF]	2 kOhm [CAT16-202J4LF]	2 kOhm [CR0805-FX-2001ELF]	2 kOhm [CRT0603-PV-2001ELF]
2 kOhm [4816P-T01-202]	2 kOhm [CAT16-202J8LF]	2 kOhm [CR0805-JW-202ELF]	2 kOhm [CRT0603-PW-2001ELF]
2 kOhm [4816P-T01-202LF]	2 kOhm [CAT25-202JALF]	2 kOhm [CR0805-JW-202GLF]	2 kOhm [CRT0805-BY-2001ELF]
2 kOhm [4816P-T02-202]	2 kOhm [CAY10-202J4LF]	2 kOhm [CR1206-FX-2001ELF]	2 kOhm [CRT1206-BY-2001ELF]
2 kOhm [4816P-T02-202LF]	2 kOhm [CAY16-2001F4LF]	2 kOhm [CR1206-FX-2001GLF]	2 kOhm [PWR220T-35-2001J]
2 kOhm [4818P-2-202]	2 kOhm [CAY16-202J2LF]	2 kOhm [CR1206-JW-202ELF]	2 kOhm [PWR221T-30-2001F]
2 kOhm [4818P-2-202LF]	2 kOhm [CAY16-202J4LF]	2 kOhm [CR1206-JW-202GLF]	2 kOhm [PWR263S-35-2001J]
2 kOhm [4818P-T02-202]	2 kOhm [CAY17-202JALF]	2 kOhm [CR2010-JW-202ELF]	2 kOhm [PWR4525W2001J]
2 kOhm [4820P-2-202]	2 kOhm [CR0201-FW-2001GLF]	2 kOhm [CR2512-FX-2001ELF]	2 kOhm [PWR4525W2001JE]
2 kOhm [4820P-2-202F]	2 kOhm [CR0201-JW-202GLF]	2 kOhm [CRM1206-FX-2001ELF]	
2 kOhm [4820P-T01-202]	2 kOhm [CR0402-FX-2001GLF]	2 kOhm [CRM2512-JW-202ELF]	2 MOhm [4116R-1-205LF]
2 kOhm [4820P-T02-202]	2 kOhm [CR0402-JW-202GLF]	2 kOhm [CRT0402-FZ-2001GLF]	2 MOhm [4608X-102-205LF]

Multisim 14.1 Base Edition Components

2 MOhm [4610X-101-205LF]	2 nF [C0603C202K3HACTU]	2 Ohm [CRL0603-JW-2R00ELF]	2 Ohm [PWR163S-25-2R00JE]
2 MOhm [4816P-1-205]	2 nF [C0603C202K5HACTU]	2 Ohm [CRL0805-FW-2R00ELF]	2 Ohm [PWR220T-20-2R00F]
2 MOhm [4816P-1-205LF]	2 nF [C1210C202KCGACTU]	2 Ohm [CRL0805-JW-2R00ELF]	2 Ohm [PWR220T-20-2R00J]
2 MOhm [CR0603-FW-2004ELF]	2 nF [C1812C202KBGACTU]	2 Ohm [CRL1206-FW-2R00ELF]	2 Ohm [PWR220T-35-2R00F]
2 MOhm [CR0603-JW-205ELF]	2 nF [C1825C202KBGACTU]	2 Ohm [CRL2010-FW-2R00ELF]	2 Ohm [PWR221T-30-2R00F]
2 MOhm [CR0805-JW-205ELF]	2 nF [C2220C202KBGACTU]	2 Ohm [CRL2010-JW-2R00ELF]	2 Ohm [PWR2615W2R00J]
2 MOhm [CR1206-FW-2004ELF]	2 nF [C2225C202KBGACTU]	2 Ohm [CRL2512-FW-2R00ELF]	2 Ohm [PWR263S-20-2R00F]
2 MOhm [CR1206-JW-205ELF]	2 Ohm [CR0402-J/-2R0GLF]	2 Ohm [CRM1206-FX-2R00ELF]	2 Ohm [PWR263S-20-2R00FE]
2 mOhm [CRE2512-FZ-R002E-2]	2 Ohm [CR0402-JW-2R0GLF]	2 Ohm [CRM2010-JW-2R0ELF]	2 Ohm [PWR263S-20-2R00J]
2 mOhm [CRE2512-FZ-R002E-3]	2 Ohm [CR0603-J/-2R0ELF]	2 Ohm [CRM2512-FX-2R00ELF]	2 Ohm [PWR263S-20-2R00JE]
2 mOhm [CRF2512-FX-R002ELF]	2 Ohm [CR0805-J/-2R0ELF]	2 Ohm [CRM2512-JW-2R0ELF]	2 Ohm [PWR263S-35-2R00F]
2 mOhm [CRF2512-JV-R002ELF]	2 Ohm [CR1206-J/-2R0ELF]	2 Ohm [CRT0805-CY-2R00ELF]	2 Ohm [PWR263S-35-2R00J]
2 MOhm [CRT1206-DZ-2004ELF]	2 Ohm [CRL0603-FW-2R00ELF]	2 Ohm [PWR163S-25-2R00F]	2 Ohm [PWR3014W2R00JE]
2 mOhm [CST0612-FC-R002E]		2 Ohm [PWR163S-25-2R00FE]	2 Ohm [PWR4318W2R00JE]
2 nF [C0603C202K1HACTU]		2 Ohm [PWR163S-25-2R00J]	

Multisim 14.1 Base Edition Components

2 Ohm [PWR5322W2R00JE]	2.1 kOhm [CR0805- FX-2101ELF]	2.2 kOhm [4116R- 1-222]	2.2 kOhm [4306R- 102-222]
2 Ohm [PWR6327N2R00F]	2.1 kOhm [CR1206- FX-2101ELF]	2.2 kOhm [4116R- 1-222LF]	2.2 kOhm [4306R- 102-222LF]
2 uH [SRP1204- 1R8M]	2.15 kOhm [CR0402-FX- 2151GLF]	2.2 kOhm [4116R- 2-222]	2.2 kOhm [4308H- 101-222]
2 uH [SRP1205- 1R8Y]	2.15 kOhm [CR0603-FX- 2151ELF]	2.2 kOhm [4116R- 2-222LF]	2.2 kOhm [4308H- 102-222]
2 uH [SRR1305- 2R0ZL]	2.15 kOhm [CR0805-FX- 2151ELF]	2.2 kOhm [4304M- 101-222]	2.2 kOhm [4308H- 102-222LF]
2 uH [SRU3014- 2R0Y]	2.15 kOhm [CR1206-FX- 2151GLF]	2.2 kOhm [4304M- 101-222LF]	2.2 kOhm [4308M- 101-222]
2.05 kOhm [CR0402-FX- 2051GLF]	2.15 kOhm [CR1206-FX- 2151ELF]	2.2 kOhm [4304M- 102-222]	2.2 kOhm [4308M- 101-222LF]
2.05 kOhm [CR0603-FX- 2051ELF]	2.15 kOhm [CRT0402-FZ- 2151GLF]	2.2 kOhm [4304M- 102-222LF]	2.2 kOhm [4308M- 102-222]
2.05 kOhm [CR0805-FX- 2051ELF]	2.2 kOhm [4108R- 1-222]	2.2 kOhm [4306H- 101-222]	2.2 kOhm [4308M- 102-222LF]
2.05 kOhm [CR1206-FX- 2051ELF]	2.2 kOhm [4108R- 1-222LF]	2.2 kOhm [4306H- 101-222LF]	2.2 kOhm [4308R- 101-222]
2.05 kOhm [CR1206-FX- 2051ELF]	2.2 kOhm [4114R- 1-222]	2.2 kOhm [4306M- 101-222]	2.2 kOhm [4308R- 101-222LF]
2.05 kOhm [CRT0402-FZ- 2051GLF]	2.2 kOhm [4114R- 1-222LF]	2.2 kOhm [4306M- 102-222]	2.2 kOhm [4308R- 102-222]
2.1 kOhm [CR0402- FX-2101GLF]	2.2 kOhm [4114R- 2-222]	2.2 kOhm [4306M- 102-222LF]	2.2 kOhm [4308R- 102-222LF]
2.1 kOhm [CR0603- FX-2101ELF]	2.2 kOhm [4114R- 2-222LF]	2.2 kOhm [4306R- 101-222]	2.2 kOhm [4309R- 101-222]
		2.2 kOhm [4306R- 101-222LF]	2.2 kOhm [4309R- 101-222LF]

Multisim 14.1 Base Edition Components

2.2 kOhm [4310H-101-222]	2.2 kOhm [4416P-T01-222]	2.2 kOhm [4606X-AP1-222LF]	2.2 kOhm [4610H-101-222LF]
2.2 kOhm [4310H-101-222LF]	2.2 kOhm [4416P-T02-222]	2.2 kOhm [4606X-AP2-222LF]	2.2 kOhm [4610H-102-222LF]
2.2 kOhm [4310H-102-222]	2.2 kOhm [4420P-2-222]	2.2 kOhm [4607M-101-222LF]	2.2 kOhm [4610M-101-222LF]
2.2 kOhm [4310M-101-222]	2.2 kOhm [4420P-T01-222]	2.2 kOhm [4607X-101-222LF]	2.2 kOhm [4610X-101-222LF]
2.2 kOhm [4310M-101-222LF]	2.2 kOhm [4420P-T02-222]	2.2 kOhm [4608H-102-222LF]	2.2 kOhm [4610X-102-222LF]
2.2 kOhm [4310M-102-222]	2.2 kOhm [4604X-101-222LF]	2.2 kOhm [4608M-101-222LF]	2.2 kOhm [4610X-AP1-222LF]
2.2 kOhm [4310M-102-222LF]	2.2 kOhm [4604X-102-222LF]	2.2 kOhm [4608M-102-222LF]	2.2 kOhm [4610X-AP2-222LF]
2.2 kOhm [4310R-101-222]	2.2 kOhm [4605M-101-222LF]	2.2 kOhm [4608X-101-222LF]	2.2 kOhm [4611X-101-222LF]
2.2 kOhm [4310R-101-222LF]	2.2 kOhm [4605X-101-222LF]	2.2 kOhm [4608X-102-222LF]	2.2 kOhm [4612X-101-222LF]
2.2 kOhm [4310R-102-222]	2.2 kOhm [4605X-AP1-222LF]	2.2 kOhm [4608X-AP1-222LF]	2.2 kOhm [4612X-102-222LF]
2.2 kOhm [4310R-102-222LF]	2.2 kOhm [4606H-101-222LF]	2.2 kOhm [4608X-AP2-222LF]	2.2 kOhm [4613X-101-222LF]
2.2 kOhm [4311R-101-222]	2.2 kOhm [4606M-101-222LF]	2.2 kOhm [4609H-101-222LF]	2.2 kOhm [4614X-102-222LF]
2.2 kOhm [4311R-101-222LF]	2.2 kOhm [4606M-102-222LF]	2.2 kOhm [4609M-101-222LF]	2.2 kOhm [4814P-1-222]
2.2 kOhm [4416P-1-222]	2.2 kOhm [4606X-101-222LF]	2.2 kOhm [4609X-101-222LF]	2.2 kOhm [4814P-1-222LF]
2.2 kOhm [4416P-2-222]	2.2 kOhm [4606X-102-222LF]	2.2 kOhm [4609X-AP1-222LF]	2.2 kOhm [4814P-2-222]

Multisim 14.1 Base Edition Components

2.2 kOhm [4814P-2-222LF]	2.2 kOhm [4820P-2-222]	2.2 kOhm [CAY16-222J8LF]	2.2 kOhm [CR2512-JW-222ELF]
2.2 kOhm [4814P-T01-222]	2.2 kOhm [4820P-2-222LF]	2.2 kOhm [CAY17-222JALF]	2.2 kOhm [CRM1206-FX-2201ELF]
2.2 kOhm [4814P-T01-222LF]	2.2 kOhm [4820P-T01-222]	2.2 kOhm [CR0402-FX-2201GLF]	2.2 kOhm [CRM1206-JW-222ELF]
2.2 kOhm [4814P-T02-222]	2.2 kOhm [4820P-T01-222LF]	2.2 kOhm [CR0402-JW-222GLF]	2.2 kOhm [CRM2512-FX-2201ELF]
2.2 kOhm [4814P-T02-222LF]	2.2 kOhm [4820P-T02-222]	2.2 kOhm [CR0603-FX-2201ELF]	2.2 kOhm [CRM2512-JW-222ELF]
2.2 kOhm [4816P-1-222]	2.2 kOhm [CAT10-222J4LF]	2.2 kOhm [CR0603-JW-222ELF]	2.2 kOhm [CRT1206-BY-2201ELF]
2.2 kOhm [4816P-1-222LF]	2.2 kOhm [CAT16-2201F4LF]	2.2 kOhm [CR0603-JW-222GLF]	2.2 kOhm [PWR163S-25-2201FE]
2.2 kOhm [4816P-2-222]	2.2 kOhm [CAT16-222J2LF]	2.2 kOhm [CR0805-FX-2201ELF]	2.2 kOhm [PWR2615W2201J]
2.2 kOhm [4816P-2-222LF]	2.2 kOhm [CAT16-222J4LF]	2.2 kOhm [CR0805-JW-222ELF]	2.2 kOhm [PWR2615W2201JE]
2.2 kOhm [4816P-T01-222]	2.2 kOhm [CAT16-222J8LF]	2.2 kOhm [CR1206-FX-2201ELF]	2.2 kOhm [PWR4525W2201J]
2.2 kOhm [4816P-T01-222LF]	2.2 kOhm [CAT25-222JALF]	2.2 kOhm [CR1206-JW-222ELF]	2.2 kOhm [PWR4525W2201JE]
2.2 kOhm [4816P-T02-222]	2.2 kOhm [CAY10-222J4LF]	2.2 kOhm [CR2010-FX-2201ELF]	2.2 kOhm [PWR6327W2201J]
2.2 kOhm [4816P-T02-222LF]	2.2 kOhm [CAY16-2201F4LF]	2.2 kOhm [CR2010-JW-222ELF]	
2.2 kOhm [4818P-T02-222]	2.2 kOhm [CAY16-222J4GLF]	2.2 kOhm [CR2512-FX-2201ELF]	
2.2 kOhm [4820P-1-222]	2.2 kOhm [CAY16-222J4LF]		

Multisim 14.1 Base Edition Components

2.2 kOhm [PWR6327W2201JE]	2.2 MOhm [4116R- 1-225LF]	2.2 MOhm [4816P- 2-225LF]	2.2 nF [0306YC222KAT2A]
2.2 mH [SDR0503- 222JL]	2.2 MOhm [4116R- 2-225]	2.2 MOhm [4816P- T01-225]	2.2 nF [0306ZC222KAT2A]
2.2 mH [SDR0805- 222KL]	2.2 MOhm [4306R- 102-225]	2.2 MOhm [CAT25- 225JALF]	2.2 nF [06125C222KAT2V]
2.2 mH [SDR0906- 222KL]	2.2 MOhm [4308R- 102-225]	2.2 MOhm [CHV2512-FX- 2204ELF]	2.2 nF [C0402C222K3RACT U]
2.2 mH [SDR1005- 222KL]	2.2 MOhm [4308R- 102-225LF]	2.2 MOhm [CR0402-JW- 225GLF]	2.2 nF [C0402C222K4RACT U]
2.2 mH [SDR1006- 222KL]	2.2 MOhm [4310R- 101-225LF]	2.2 MOhm [CR0603-JW- 225ELF]	2.2 nF [C0402C222K5RACT U]
2.2 mH [SRE6603- 222M]	2.2 MOhm [4605X- 101-225LF]	2.2 MOhm [CR0805-FX- 2204ELF]	2.2 nF [C0402C222K8RACT U]
2.2 mH [SRR0604- 222KL]	2.2 MOhm [4606X- 101-225LF]	2.2 MOhm [CR0805-JW- 225ELF]	2.2 nF [C0603C222K1HACT U]
2.2 mH [SRR0906- 222YL]	2.2 MOhm [4608X- 101-225LF]	2.2 MOhm [CR1206-FW- 2204ELF]	2.2 nF [C0603C222K1RACT U]
2.2 mH [SRR0908- 222YL]	2.2 MOhm [4608X- 102-225LF]	2.2 MOhm [CR1206-JW- 225ELF]	2.2 nF [C0603C222K2RACT U]
2.2 mH [SRR1005- 222K]	2.2 MOhm [4609X- 101-225LF]	2.2 MOhm [CR1206-JW- 225GLF]	2.2 nF [C0603C222K3GACT U]
2.2 mH [SRR1208- 222KL]	2.2 MOhm [4610X- 101-225LF]	2.2 nF [03063C222KAT2A]	2.2 nF [C0603C222K3HACT U]
2.2 mH [SRR6603- 222ML]	2.2 MOhm [4610X- 102-225LF]		
2.2 MOhm [4114R- 2-225]	2.2 MOhm [4816P- 2-225]		
2.2 MOhm [4116R- 1-225]			

Multisim 14.1 Base Edition Components

2.2 nF [C0603C222K3RACT U]	2.2 nF [C0805C222K3HACT U]	2.2 nF [C1210C222K1GACT U]	2.2 nF [CA064C222K1RACT U]
2.2 nF [C0603C222K4RACT U]	2.2 nF [C0805C222K3RACT U]	2.2 nF [C1210C222K1RACT U]	2.2 nF [CA064C222K4RACT U]
2.2 nF [C0603C222K5HACT U]	2.2 nF [C0805C222K5HACT U]	2.2 nF [C1210C222K2GACT U]	2.2 nF [CA064C222K5RACT U]
2.2 nF [C0603C222K5RACT U]	2.2 nF [C0805C222K5RACT U]	2.2 nF [C1210C222K5GACT U]	2.2 nF [GMC5.7222K100J3 1TR12]
2.2 nF [C0603C222K8RACT U]	2.2 nF [C0805C222KARACT U]	2.2 nF [C1210C222KCGAC TU]	2.2 nF [GMC5.7222K50J31 TR12]
2.2 nF [C0603C222K9RACT U]	2.2 nF [C1206C222K1GACT U]	2.2 nF [C1812C222K2GACT U]	2.2 nF [GMC5.7223K250J3 5TR12]
2.2 nF [C0805C222K1GACT U]	2.2 nF [C1206C222K1RACT U]	2.2 nF [C1812C222KBGAC TU]	2.2 nF [GMC7.3222K100K3 1TR12]
2.2 nF [C0805C222K1HACT U]	2.2 nF [C1206C222K2RACT U]	2.2 nF [C1812C222KDGAC TU]	2.2 nF [GMC7.3222K400K3 1TR12]
2.2 nF [C0805C222K1RACT U]	2.2 nF [C1206C222K4RACT U]	2.2 nF [C1825C222KBGAC TU]	2.2 nF [GMC7.3223K100K3 1TR12]
2.2 nF [C0805C222K2RACT U]	2.2 nF [C1206C222K5GACT U]	2.2 nF [C2220C222KBGAC TU]	2.2 nF [GMC7.3223K250K3 3TR12]
2.2 nF [C0805C222K3GACT U]	2.2 nF [C1206C222K5RACT U]	2.2 nF [C2225C222KBGAC TU]	2.2 nF [GPC7.3222K160K3 1TR12]

Multisim 14.1 Base Edition Components

2.2 nF [GPC7.3222K630K3 3TR12]	2.2 nF [SPC7.3222K100K31 TR12]	2.2 Ohm [CRL0603- FW-2R20ELF]	2.2 Ohm [PWR163S-25- 2R20F]
2.2 nF [GPC7.3222K63K31 TR12]	2.2 nF [SPC7.3222K250K31 TR12]	2.2 Ohm [CRL0603- JW-2R20ELF]	2.2 Ohm [PWR163S-25- 2R20J]
2.2 nF [LD17YC222KAB2S]	2.2 nF [SPC7.3222K400K31 TR12]	2.2 Ohm [CRL0805- FW-2R20ELF]	2.2 Ohm [PWR163S-25- 2R20JE]
2.2 nF [MMC5.7222K100J 31TR12]	2.2 nF [SPC7.3222K630K33 TR12]	2.2 Ohm [CRL1206- FW-2R20ELF]	2.2 Ohm [PWR2010W2R20JE]
2.2 nF [MMC5.7222K250J 31TR12]	2.2 nF [W2F15C2228AT1A]	2.2 Ohm [CRL1206- JW-2R20ELF]	2.2 Ohm [PWR220T-35- 2R20J]
2.2 nF [MMC5.7222K50J3 1TR12]	2.2 nF [W3F15C2228AT1A]	2.2 Ohm [CRL2010- JW-2R20ELF]	2.2 Ohm [PWR221T-30- 2R20F]
2.2 nF [MMC7.3222K100K 31TR12]	2.2 Ohm [CR0402- J/-2R2GLF]	2.2 Ohm [CRL2512- FW-2R20ELF]	2.2 Ohm [PWR221T-30- 2R20J]
2.2 nF [MMC7.3222K250K 31TR12]	2.2 Ohm [CR0603- J/-2R2ELF]	2.2 Ohm [CRM1206-FX- 2R20ELF]	2.2 Ohm [PWR2615W2R20J]
2.2 nF [MMC7.3222K400K 31TR12]	2.2 Ohm [CR0603- J/-2R2GLF]	2.2 Ohm [CRM1206-JW- 2R2ELF]	2.2 Ohm [PWR263S-20- 2R20F]
2.2 nF [MMC7.3222K50K3 1TR12]	2.2 Ohm [CR0805- J/-2R2ELF]	2.2 Ohm [CRM2010-JW- 2R2ELF]	2.2 Ohm [PWR263S-20- 2R20J]
2.2 nF [MMC7.3222K63K3 1TR12]	2.2 Ohm [CR1206- J/-2R2ELF]	2.2 Ohm [CRM2512-JW- 2R2ELF]	2.2 Ohm [PWR263S-20- 2R20JE]
	2.2 Ohm [CR2010- J/-2R2ELF]		
	2.2 Ohm [CR2512- J/-2R2ELF]		

Multisim 14.1 Base Edition Components

2.2 Ohm [PWR263S-35- 2R20J]	2.2 uF [C0805C225K4PACT U]	2.2 uF [C1206C225K4RACT U]	2.2 uF [C1210C225K8RACT U]
2.2 Ohm [PWR3014WA2R20J E]	2.2 uF [C0805C225K4RACT U]	2.2 uF [C1206C225K8PACT U]	2.2 uF [C1210C225K9PACT U]
2.2 Ohm [PWR4318W2R20JE]	2.2 uF [C0805C225K8PACT U]	2.2 uF [C1206C225K8RACT U]	2.2 uF [C1210C225K9RACT U]
2.2 Ohm [PWR4525W2R20J]	2.2 uF [C0805C225K8RACT U]	2.2 uF [C1206C225K9PACT U]	2.2 uF [C1210C225M8VAC TU]
2.2 Ohm [PWR6327W2R20F]	2.2 uF [C0805C225K9PACT U]	2.2 uF [C1206C225K9RACT U]	2.2 uF [C1812C225K1RACT U]
2.2 Ohm [PWR6327W2R20F E]	2.2 uF [C0805C225K9RACT U]	2.2 uF [C1206C225M4VAC TU]	2.2 uF [C1825C225K5RACT U]
2.2 Ohm [PWR6327W2R20J]			
2.2 uF [0612ZC225KAT2A]	2.2 uF [C0805C225M4VAC TU]	2.2 uF [C1210C225K1RACT U]	2.2 uF [C2220C225K5RACT U]
2.2 uF [C0402C225K9PACT U]	2.2 uF [C0805C225M8VAC TU]	2.2 uF [C1210C225K3PACT U]	2.2 uF [C2225C225K5RACT U]
2.2 uF [C0603C225K4PACT U]	2.2 uF [C1206C225K3NAC TU]	2.2 uF [C1210C225K3RACT U]	2.2 uF [C2225C225M5UAC TU]
2.2 uF [C0603C225K8PACT U]	2.2 uF [C1206C225K3PACT U]	2.2 uF [C1210C225K4RACT U]	2.2 uF [LD186C225KAB2A]
2.2 uF [C0603C225K9PACT U]	2.2 uF [C1206C225K4PACT U]	2.2 uF [C1210C225K5RACT U]	2.2 uF [LD18ZC225KAB2A]
			2.2 uF [LGC24D225MAT2S 1]

Multisim 14.1 Base Edition Components

2.2 uF [MDC10225K100A5 2P3TUBE]	2.2 uF [T491A225M006AT]	2.2 uF [T494A225M010AT]	2.2 uF [TACL225K004RTA]
2.2 uF [MDC10225K50A52 P3TUBE]	2.2 uF [T491A225M010AT]	2.2 uF [T494A225M016AT]	2.2 uF [TACL225K006RTA]
2.2 uF [MDC15225K100B5 3P3TUBE]	2.2 uF [T491A225M016AT]	2.2 uF [T494A225M020AT]	2.2 uF [TACL225K010RTA]
2.2 uF [MDC15225K50B53 P3TUBE]	2.2 uF [T491A225M020AT]	2.2 uF [T494B225M020AT]	2.2 uF [TAJA225K006RNJ]
2.2 uF [MDK10225K50A52 P3TUBE]	2.2 uF [T491A225M025AT]	2.2 uF [T494B225M025AT]	2.2 uF [TAJA225K010RNJ]
2.2 uF [MDK10225K50A52 P3TUBE]	2.2 uF [T491B225M010AT]	2.2 uF [T494B225M035AT]	2.2 uF [TAJA225K016RNJ]
2.2 uF [MDS10225K50A52 P3TUBE]	2.2 uF [T491B225M020AT]	2.2 uF [T494C225M025AT]	2.2 uF [TAJA225K020RNJ]
2.2 uF [MDS15225K100B5 3P3TUBE]	2.2 uF [T491B225M025AT]	2.2 uF [T494C225M035AT]	2.2 uF [TAJA225K025RNJ]
2.2 uF [PGC24D225MAB2S 1]	2.2 uF [T491B225M035AT]	2.2 uF [T494C225M050AT]	2.2 uF [TAJA225K035RNJ]
2.2 uF [T409C225M015AH 4250]	2.2 uF [T491C225M025AT]	2.2 uF [T494D225M050AT]	2.2 uF [TAJB225K016RNJ]
2.2 uF [T429A225M010AH 4250]	2.2 uF [T491C225M035AT]	2.2 uF [T494S225M016AT]	2.2 uF [TAJB225K020RNJ]
2.2 uF [T429C225M015AH 4250]	2.2 uF [T491C225M050AT]	2.2 uF [T498A225M010AT E4K6]	2.2 uF [TAJB225K025RNJ]
2.2 uF [T429C225M015AH 4250]	2.2 uF [T491D225M050AT]	2.2 uF [T498B225M025AT E3K0]	2.2 uF [TAJB225K035RNJ]
2.2 uF [T429C225M015AH 4250]	2.2 uF [T491S225M016AT]	2.2 uF [TACL225K003RTA]	2.2 uF [TAJC225K035RNJ]
	2.2 uF [T494A225M006AT]		2.2 uF [TAJC225K050RNJ]

Multisim 14.1 Base Edition Components

2.2 uF [TAJD225K050RNJ]	2.2 uF [THJA225K016RJN]	2.2 uF [TPSC225K050R150 0]	2.2 uH [SDR0703- 2R2ML]
2.2 uF [TAJP225K020RNJ]	2.2 uF [THJB225K025RJN]	2.2 uF [TPSD225K050R120 0]	2.2 uH [SDR0906- 2R2ML]
2.2 uF [TAJR225K004RNJ]	2.2 uF [THJC225K035RJN]		2.2 uH [SDR1005- 2R2ML]
2.2 uF [TAJR225K006RNJ]	2.2 uF [TPSA225K010R180 0]	2.2 uF [TPSR225K006R700 0]	2.2 uH [SDR1006- 2R2ML]
2.2 uF [TAJR225K010RNJ]	2.2 uF [TPSA225K016R180 0]	2.2 uF [TPST225K016R200 0]	2.2 uH [SDR1307- 2R2ML]
2.2 uF [TAJR225K016RNJ]	2.2 uF [TPSA225K016R350 0]	2.2 uF [TRJA225K016RRJ]	2.2 uH [SDR1307A- 2R2M]
2.2 uF [TAJS225K004RNJ]	2.2 uF [TPSA225K020R300 0]	2.2 uF [TRJA225K025RRJ]	2.2 uH [SDR1806- 2R2ML]
2.2 uF [TAJS225K006RNJ]	2.2 uF [TPSA225K025R250 0]	2.2 uF [TRJD225K050R120 0]	2.2 uH [SDR6603- 2R2M]
2.2 uF [TAJS225K010RNJ]	2.2 uF [TPSB225K025R120 0]	2.2 uH [SDE0403A- 2R2M]	2.2 uH [SDR7030- 2R2M]
2.2 uF [TAJS225K016RNJ]	2.2 uF [TPSB225K025R250 0]	2.2 uH [SDE0604A- 2R2M]	2.2 uH [SDR7045- 2R2M]
2.2 uF [TAJT225K016RNJ]	2.2 uF [TPSB225K035R200 0]	2.2 uH [SDE1006A- 2R2M]	2.2 uH [SRN2010- 2R2M]
2.2 uF [TAJT225K020RNJ]	2.2 uF [TPSC225K035R100 0]	2.2 uH [SDR0302- 2R2ML]	2.2 uH [SRN2012- 2R2M]
2.2 uF [TAJT225K025RNJ]		2.2 uH [SDR0403- 2R2ML]	2.2 uH [SRN2510- 2R2M]
2.2 uF [TAJT225K035RNJ]		2.2 uH [SDR0604- 2R2ML]	2.2 uH [SRN2512- 2R2M]
			2.2 uH [SRN3010- 2R2M]

Multisim 14.1 Base Edition Components

2.2 uH [SRN3015-2R2M]	2.2 uH [SRP1265A-2R2M]	2.2 uH [SRR0805-2R2M]	2.2 uH [SRU1038-2R2Y]
2.2 uH [SRN4012T-2R2M]	2.2 uH [SRP1270-2R2M]	2.2 uH [SRR1003-2R2M]	2.2 uH [SRU1038A-2R2Y]
2.2 uH [SRN4018-2R2M]	2.2 uH [SRP1770TA-2R2M]	2.2 uH [SRR1005-2R2M]	2.2 uH [SRU1048-2R2Y]
2.2 uH [SRN4026-2R2Y]	2.2 uH [SRP4012TA-2R2M]	2.2 uH [SRR1210-2R2Y]	2.2 uH [SRU1048A-2R2Y]
2.2 uH [SRN5020-2R2Y]	2.2 uH [SRP4020-2R2M]	2.2 uH [SRR1210A-2R2Y]	2.2 uH [SRU1063-2R2Y]
2.2 uH [SRN5040-2R2Y]	2.2 uH [SRP4020TA-2R2M]	2.2 uH [SRR1260-2R2Y]	2.2 uH [SRU2009-2R2Y]
2.2 uH [SRN6028-2R2Y]	2.2 uH [SRP5015TA-2R2M]	2.2 uH [SRR1260A-2R2Y]	2.2 uH [SRU2011-2R2Y]
2.2 uH [SRN6045-2R2Y]	2.2 uH [SRP5030T-2R2M]	2.2 uH [SRR4011-2R2YL]	2.2 uH [SRU2013-2R2Y]
2.2 uH [SRN8040-2R2Y]	2.2 uH [SRP5030TA-2R2M]	2.2 uH [SRR4018-2R2Y]	2.2 uH [SRU2016-2R2Y]
2.2 uH [SRP1038A-2R2M]	2.2 uH [SRP6540-2R2M]	2.2 uH [SRR4028-2R2Y]	2.2 uH [SRU3011-2R2Y]
2.2 uH [SRP1040-2R2M]	2.2 uH [SRP7028A-2R2M]	2.2 uH [SRR6603-2R2ML]	2.2 uH [SRU3017-2R2Y]
2.2 uH [SRP1045-2R2M]	2.2 uH [SRP7030-2R2FM]	2.2 uH [SRR7032-2R2M]	2.2 uH [SRU5018-2R2Y]
2.2 uH [SRP1206-2R0Y]	2.2 uH [SRP7050TA-2R2M]	2.2 uH [SRR7045-2R2M]	2.2 uH [SRU5028-2R2Y]
2.2 uH [SRP1235-2R2M]	2.2 uH [SRR0604-2R2ML]	2.2 uH [SRU1028-2R2Y]	2.2 uH [SRU5028A-2R2Y]
2.2 uH [SRP1250-2R2M]	2.2 uH [SRR0618-2R2ML]	2.2 uH [SRU1028A-2R2Y]	2.2 uH [SRU6025-2R2Y]

Multisim 14.1 Base Edition Components

2.2 uH [SRU6025A-2R2Y]	2.21 kOhm [CRT0603-CY-2211ELF]	2.26 kOhm [CRT0805-BY-2261ELF]	2.37 kOhm [CR0603-FX-2371ELF]
2.2 uH [SRU8043-2R2Y]	2.21 kOhm [CRT0805-FX-2211ELF]	2.26 kOhm [CRT0805-FV-2261ELF]	2.37 kOhm [CR0805-FX-2371ELF]
2.21 kOhm [CAT16-2211F4LF]	2.21 kOhm [CRT1206-BY-2211ELF]	2.26 kOhm [CRT1206-FZ-2261ELF]	2.37 kOhm [CR1206-FX-2371ELF]
2.21 kOhm [CAY16-2211F4LF]	2.21 MOhm [CR0805-FX-2214ELF]	2.3 kOhm [4116R-1-232]	2.37 kOhm [CR2512-FX-2371ELF]
2.21 kOhm [CR0402-FX-2211GLF]	2.21 Ohm [CRM1206-FX-2R21ELF]	2.3 kOhm [4116R-1-232LF]	2.37 kOhm [CRT0402-FZ-2371GLF]
2.21 kOhm [CR0603-FX-2211ELF]	2.26 kOhm [CR0402-FX-2261GLF]	2.32 kOhm [CR0402-FX-2321GLF]	2.4 kOhm [4114R-1-242]
2.21 kOhm [CR0603-FX-2211GLF]	2.26 kOhm [CR0603-FX-2261ELF]	2.32 kOhm [CR0603-FX-2321ELF]	2.4 kOhm [4114R-1-242LF]
2.21 kOhm [CR0805-FX-2211ELF]	2.26 kOhm [CR0805-FX-2261ELF]	2.32 kOhm [CR0805-FX-2321ELF]	2.4 kOhm [4116R-1-242]
2.21 kOhm [CR1206-FX-2211ELF]	2.26 kOhm [CR1206-FX-2261ELF]	2.32 kOhm [CR1206-FX-2321ELF]	2.4 kOhm [4116R-1-242LF]
2.21 kOhm [CRM1206-FX-2211ELF]	2.26 kOhm [CR1206-FX-2261ELF]	2.32 kOhm [CRT0805-BX-2321ELF]	2.4 kOhm [CAT16-2401F4LF]
2.21 kOhm [CRT0603-BY-2211ELF]	2.26 kOhm [CRT0402-FZ-2261GLF]	2.37 kOhm [CAY16-2371F4LF]	2.4 kOhm [CAY10-242J4LF]
2.21 kOhm [CRT0603-CW-2211ELF]	2.26 kOhm [CRT0603-CY-2261ELF]	2.37 kOhm [CR0402-FX-2371GLF]	2.4 kOhm [CAY16-242J4LF]

Multisim 14.1 Base Edition Components

2.4 kOhm [CR0402-FX-2401GLF]	2.4 kOhm [CRT0805-FV-2401ELF]	2.4 nF [C0805C242K5HACTU]	2.4 Ohm [CRL2010-FW-2R40ELF]
2.4 kOhm [CR0402-JW-242GLF]	2.4 MOhm [4116R-1-245LF]	2.4 nF [C1825C242KBGAC TU]	2.4 Ohm [CRL2010-JW-2R40ELF]
2.4 kOhm [CR0603-FX-2401ELF]	2.4 MOhm [CR0603-JW-245ELF]	2.4 nF [C2220C242KBGAC TU]	2.4 Ohm [CRL2512-FW-2R40ELF]
2.4 kOhm [CR0603-JW-242ELF]	2.4 MOhm [CR0805-JW-245ELF]	2.4 nF [C2225C242KBGAC TU]	2.4 Ohm [CRL2512-JW-2R40ELF]
2.4 kOhm [CR0805-FX-2401ELF]	2.4 MOhm [CR1206-JW-245ELF]	2.4 Ohm [CR0603-J/-2R4ELF]	2.4 Ohm [CRM2512-JW-2R4ELF]
2.4 kOhm [CR0805-JW-242ELF]	2.4 nF [C0603C242K1HACTU]	2.4 Ohm [CR0805-J/-2R4ELF]	2.4 Ohm [PWR263S-35-2R40J]
2.4 kOhm [CR1206-FX-2401ELF]	2.4 nF [C0603C242K3HACTU]	2.4 Ohm [CR1206-J/-2R4ELF]	2.4 uH [SRR1240-2R4Y]
2.4 kOhm [CR1206-JW-242ELF]	2.4 nF [C0603C242K5HACTU]	2.4 Ohm [CRL0603-FW-2R40ELF]	2.4 uH [SRR1260-2R4Y]
2.4 kOhm [CR2010-JW-242ELF]	2.4 nF [C0805C242K1GACTU]	2.4 Ohm [CRL0603-JW-2R40ELF]	2.4 uH [SRR1260A-2R4Y]
2.4 kOhm [CR2512-JW-242ELF]	2.4 nF [C0805C242K1HACTU]	2.4 Ohm [CRL0805-FW-2R40ELF]	2.43 kOhm [CR0402-FX-2431GLF]
2.4 kOhm [CRM1206-JW-242ELF]	2.4 nF [C0805C242K3HACTU]	2.4 Ohm [CRL1206-FW-2R40ELF]	2.43 kOhm [CR0603-FX-2431ELF]
2.4 kOhm [CRM2010-JW-242ELF]	2.4 nF [C0805C242K3HACTU]	2.4 Ohm [CRL1206-JW-2R40ELF]	2.43 kOhm [CR0805-FX-2431ELF]
2.4 kOhm [CRT0805-BV-2401ELF]			
2.4 kOhm [CRT0805-BW-2401ELF]			

Multisim 14.1 Base Edition Components

2.43 kOhm [CR1206-FX- 2431ELF]	2.49 kOhm [CRT0805-BV- 2491ELF]	2.5 Ohm [PWR220T-20- 2R50J]	2.5 uH [SRP7028A- 2R5M]
2.49 kOhm [CAT16- 2491F4LF]	2.5 kOhm [4108R- 1-252]	2.5 Ohm [PWR220T-35- 2R50F]	2.5 uH [SRR0603- 2R5ML]
2.49 kOhm [CR0201-FW- 2491GLF]	2.5 kOhm [4108R- 1-252LF]	2.5 Ohm [PWR221T-30- 2R50F]	2.5 uH [SRR0604- 2R5ML]
2.49 kOhm [CR0402-FX- 2491GLF]	2.5 kOhm [4116R- 1-252]	2.5 Ohm [PWR263S-20- 2R50F]	2.5 uH [SRR1205- 2R5ML]
2.49 kOhm [CR0603-FX- 2491ELF]	2.5 kOhm [4116R- 1-252LF]	2.5 Ohm [PWR263S-20- 2R50F]	2.5 uH [SRR1206- 2R5ML]
2.49 kOhm [CR0603-FX- 2491ELF]	2.5 kOhm [PWR220T-35- 2501F]	2.5 Ohm [PWR263S-20- 2R50J]	2.5 uH [SRR1208- 2R5ML]
2.49 kOhm [CR0805-FX- 2491ELF]	2.5 kOhm [PWR220T-35- 2501J]	2.5 Ohm [PWR263S-35- 2R50F]	2.5 uH [SRR3011- 2R5YL]
2.49 kOhm [CR1206-FX- 2491ELF]	2.5 kOhm [PWR263S-35- 2501F]	2.5 Ohm [PWR263S-35- 2R50J]	2.5 uH [SRR5018- 2R5Y]
2.49 kOhm [CR2010-FX- 2491ELF]	2.5 kOhm [PWR6327W2501J]	2.5 uH [SDE0805A- 2R5M]	2.5 uH [SRR6028- 2R5Y]
2.49 kOhm [CRT0603-BV- 2491ELF]	2.5 Ohm [PWR163S-25- 2R50F]	2.5 uH [SDR0603- 2R5ML]	2.5 uH [SRU1038- 2R5Y]
2.49 kOhm [CRT0603-BY- 2491ELF]	2.5 Ohm [PWR163S-25- 2R50J]	2.5 uH [SDR0805- 2R5ML]	2.5 uH [SRU5011- 2R5Y]
2.49 kOhm [CRT0603-CY- 2491ELF]	2.5 Ohm [PWR220T-20- 2R50F]	2.5 uH [SDR1005- 2R5ML]	2.5 uH [SRU8028- 2R5Y]
		2.5 uH [SDR1305- 2R5Y]	2.55 kOhm [CR0402-FX- 2551GLF]
		2.5 uH [SRP1040- 2R5M]	2.55 kOhm [CR0603-FX- 2551ELF]

Multisim 14.1 Base Edition Components

2.55 kOhm [CR0805-FX- 2551ELF]	2.61 kOhm [CRT0603-FY- 2611ELF]	2.7 kOhm [4116R- 2-272]	2.7 kOhm [4308R- 101-272LF]
2.55 kOhm [CR1206-FX- 2551ELF]	2.61 kOhm [CRT0805-CX- 2611ELF]	2.7 kOhm [4116R- 2-272LF]	2.7 kOhm [4308R- 102-272]
2.55 kOhm [CR2010-FX- 2551ELF]	2.61 Ohm [CRM1206-FX- 2R61ELF]	2.7 kOhm [4306M- 101-272]	2.7 kOhm [4308R- 102-272LF]
2.55 kOhm [CRT0603-FY- 2551ELF]	2.67 kOhm [CR0402-FX- 2671GLF]	2.7 kOhm [4306M- 102-272]	2.7 kOhm [4309R- 101-272LF]
2.6 uH [SRR5028- 2R6Y]	2.67 kOhm [CR0603-FX- 2671ELF]	2.7 kOhm [4306M- 102-272LF]	2.7 kOhm [4309R- 101-272LF]
2.61 kOhm [CR0402-FX- 2611GLF]	2.67 kOhm [CR0805-FX- 2671ELF]	2.7 kOhm [4306M- 102-272LF]	2.7 kOhm [4310H- 101-272]
2.61 kOhm [CR0603-FX- 2611ELF]	2.67 kOhm [CR1206-FX- 2671ELF]	2.7 kOhm [4306R- 101-272]	2.7 kOhm [4310H- 101-272LF]
2.61 kOhm [CR0805-FX- 2611ELF]	2.7 kOhm [4114R- 1-272]	2.7 kOhm [4306R- 102-272]	2.7 kOhm [4310M- 101-272]
2.61 kOhm [CR1206-FX- 2611ELF]	2.7 kOhm [4114R- 1-272LF]	2.7 kOhm [4306R- 102-272LF]	2.7 kOhm [4310M- 101-272LF]
2.61 kOhm [CRM1206-FX- 2611ELF]	2.7 kOhm [4114R- 2-272]	2.7 kOhm [4306R- 102-272LF]	2.7 kOhm [4310M- 102-272]
2.61 kOhm [CRT0402-FZ- 2611GLF]	2.7 kOhm [4114R- 2-272LF]	2.7 kOhm [4306R- 102-272LF]	2.7 kOhm [4310M- 102-272]
	2.7 kOhm [4116R- 1-272]	2.7 kOhm [4306R- 102-272LF]	2.7 kOhm [4310M- 102-272]
	2.7 kOhm [4116R- 1-272LF]	2.7 kOhm [4308H- 101-272]	2.7 kOhm [4310R- 101-272]
		2.7 kOhm [4308H- 101-272LF]	2.7 kOhm [4310R- 101-272LF]
		2.7 kOhm [4308M- 102-272]	2.7 kOhm [4310R- 102-272]
		2.7 kOhm [4308M- 102-272LF]	2.7 kOhm [4310R- 102-272LF]
		2.7 kOhm [4308R- 101-272]	2.7 kOhm [4416P- 2-272]

Multisim 14.1 Base Edition Components

2.7 kOhm [4420P-2-272]	2.7 kOhm [4608X-AP2-272LF]	2.7 kOhm [4814P-1-272LF]	2.7 kOhm [4820P-2-272]
2.7 kOhm [4420P-T02-272]	2.7 kOhm [4609H-101-272LF]	2.7 kOhm [4814P-2-272]	2.7 kOhm [4820P-T02-272]
2.7 kOhm [4604X-101-272LF]	2.7 kOhm [4609M-101-272LF]	2.7 kOhm [4814P-2-272LF]	2.7 kOhm [CAT10-272J4LF]
2.7 kOhm [4604X-102-272LF]	2.7 kOhm [4609X-101-272LF]	2.7 kOhm [4814P-T01-272]	2.7 kOhm [CAT16-2701F4LF]
2.7 kOhm [4605X-101-272LF]	2.7 kOhm [4609X-AP1-272LF]	2.7 kOhm [4814P-T01-272LF]	2.7 kOhm [CAT16-272J4LF]
2.7 kOhm [4606H-101-272LF]	2.7 kOhm [4610H-101-272LF]	2.7 kOhm [4814P-T02-272]	2.7 kOhm [CAT16-272J8LF]
2.7 kOhm [4606M-102-272LF]	2.7 kOhm [4610H-102-272LF]	2.7 kOhm [4814P-T02-272LF]	2.7 kOhm [CAT25-272JALF]
2.7 kOhm [4606X-101-272LF]	2.7 kOhm [4610M-101-272LF]	2.7 kOhm [4816P-1-272]	2.7 kOhm [CAY10-272J4LF]
2.7 kOhm [4606X-102-272LF]	2.7 kOhm [4610X-101-272LF]	2.7 kOhm [4816P-1-272LF]	2.7 kOhm [CAY16-2701F4LF]
2.7 kOhm [4606X-AP1-272LF]	2.7 kOhm [4610X-102-272LF]	2.7 kOhm [4816P-2-272]	2.7 kOhm [CAY16-272J4LF]
2.7 kOhm [4607X-101-272LF]	2.7 kOhm [4610X-AP1-272LF]	2.7 kOhm [4816P-2-272LF]	2.7 kOhm [CAY16-272J8LF]
2.7 kOhm [4608H-101-272LF]	2.7 kOhm [4610X-AP2-272LF]	2.7 kOhm [4816P-T01-272]	2.7 kOhm [CAY17-272JALF]
2.7 kOhm [4608H-102-272LF]	2.7 kOhm [4611X-101-272LF]	2.7 kOhm [4816P-T01-272LF]	2.7 kOhm [CR0201-FW-2701GLF]
2.7 kOhm [4608X-101-272LF]	2.7 kOhm [4614X-102-272LF]	2.7 kOhm [4816P-T02-272]	2.7 kOhm [CR0402-FX-2701GLF]
2.7 kOhm [4608X-102-272LF]	2.7 kOhm [4814P-1-272]	2.7 kOhm [4816P-T02-272LF]	2.7 kOhm [CR0402-JW-272GLF]

Multisim 14.1 Base Edition Components

2.7 kOhm [CR0603-FX-2701ELF]	2.7 kOhm [CRT0603-BX-2701ELF]	2.7 MOhm [4116R-1-275]	2.7 nF [C0603C272K3HACT U]
2.7 kOhm [CR0603-FX-2701HLF]	2.7 kOhm [CRT0603-BY-2701ELF]	2.7 MOhm [4116R-1-275LF]	2.7 nF [C0603C272K3RACT U]
2.7 kOhm [CR0603-JW-272ELF]	2.7 kOhm [CRT0805-FX-2701ELF]	2.7 MOhm [CAT25-275JALF]	2.7 nF [C0603C272K4RACT U]
2.7 kOhm [CR0603-JW-272GLF]	2.7 kOhm [CRT1206-BY-2701ELF]	2.7 MOhm [CR0603-JW-275ELF]	2.7 nF [C0603C272K5HACT U]
2.7 kOhm [CR0805-FX-2701ELF]	2.7 kOhm [PWR2615W2701F]	2.7 MOhm [CR1206-JW-275ELF]	2.7 nF [C0603C272K5RACT U]
2.7 kOhm [CR0805-JW-272ELF]	2.7 kOhm [PWR2615W2701J]	2.7 nF [C0402C272K3RACT U]	2.7 nF [C0603C272K8RACT U]
2.7 kOhm [CR0805-JW-272GLF]	2.7 mF [2R5SVPC2700M]	2.7 nF [C0402C272K4RACT U]	2.7 nF [C0805C272K1GACT U]
2.7 kOhm [CR1206-FX-2701ELF]	2.7 mH [SDR0503-272JL]	2.7 nF [C0402C272K5RACT U]	2.7 nF [C0805C272K1HACT U]
2.7 kOhm [CR1206-JW-272ELF]	2.7 mH [SDR0805-272KL]	2.7 nF [C0603C272K1HACT U]	2.7 nF [C0805C272K2RACT U]
2.7 kOhm [CR1206-JW-272GLF]	2.7 mH [SDR0906-272KL]	2.7 nF [C0603C272K3GACT U]	
2.7 kOhm [CR2512-JW-272ELF]	2.7 mH [SDR1006-272KL]		
2.7 kOhm [CRM1206-FX-2701ELF]	2.7 mH [SRR0906-272YL]		
2.7 kOhm [CRM1206-JW-272ELF]	2.7 mH [SRR1005-272K]		
2.7 kOhm [CRM2512-JW-272ELF]	2.7 mH [SRR1208-272KL]		

Multisim 14.1 Base Edition Components

2.7 nF [C0805C272K3HACT U]	2.7 nF [C1206C272K5RACT U]	2.7 nF [GMC5.7273K100J3 3TR12]	2.7 nF [MMC7.3272K50K3 1TR12]
2.7 nF [C0805C272K3RACT U]	2.7 nF [C1210C272K2GACT U]	2.7 nF [GMC7.3272K100K3 1TR12]	2.7 nF [MMC7.3272K63K3 1TR12]
2.7 nF [C0805C272K4GACT U]	2.7 nF [C1210C272K5GACT U]	2.7 nF [GMC7.3272K400K3 1TR12]	2.7 Ohm [CR0402- J/-2R7GLF]
2.7 nF [C0805C272K4RACT U]	2.7 nF [C1210C272KCGAC TU]	2.7 nF [GMC7.3273K100K3 1TR12]	2.7 Ohm [CR0603- J/-2R7ELF]
2.7 nF [C0805C272K5HACT U]	2.7 nF [C1812C272K1GACT U]	2.7 nF [GMC7.3273K250K3 5TR12]	2.7 Ohm [CR0805- J/-2R7ELF]
2.7 nF [C0805C272K5RACT U]	2.7 nF [C1812C272K5GACT U]	2.7 nF [MMC5.7272K100J 31TR12]	2.7 Ohm [CR2010- J/-2R7ELF]
2.7 nF [C0805C272KARACT U]	2.7 nF [C1825C272KBGAC TU]	2.7 nF [MMC5.7272K250J 31TR12]	2.7 Ohm [CRL0603- FW-2R70ELF]
2.7 nF [C1206C272K1GACT U]	2.7 nF [C2220C272KBGAC TU]	2.7 nF [MMC5.7272K50J3 1TR12]	2.7 Ohm [CRL0805- FW-2R70ELF]
2.7 nF [C1206C272K1RACT U]	2.7 nF [C2225C272KBGAC TU]	2.7 nF [MMC7.3272K100K 31TR12]	2.7 Ohm [CRL0805- JW-2R70ELF]
2.7 nF [C1206C272K2RACT U]	2.7 nF [GMC5.7272K100J3 1TR12]	2.7 nF [MMC7.3272K250K 31TR12]	2.7 Ohm [CRL1206- FW-2R70ELF]
2.7 nF [C1206C272K5GACT U]	2.7 nF [GMC5.7272K50J31 TR12]	2.7 nF [MMC7.3272K400K 31TR12]	2.7 Ohm [CRL2010- FW-2R70ELF]
			2.7 Ohm [CRL2010- JW-2R70ELF]

Multisim 14.1 Base Edition Components

2.7 Ohm [CRL2512-FW-2R70ELF]	2.7 uF [MDC10275K100A52P3TUBE]	2.7 uH [SDR1030-2R7M]	2.74 kOhm [CR0603-FX-2741ELF]
2.7 Ohm [CRM1206-JW-2R7ELF]	2.7 uF [MDC10275K50A52P3TUBE]	2.7 uH [SDR1045-2R7M]	2.74 kOhm [CR0805-FX-2741ELF]
2.7 Ohm [CRM2512-JW-2R7ELF]	2.7 uF [MDC15275K100B53P3TUBE]	2.7 uH [SDR1307-2R7ML]	2.74 kOhm [CR1206-FX-2741ELF]
2.7 Ohm [PWR5322W2R70JE]	2.7 uF [MDC15275K50B53P3TUBE]	2.7 uH [SDR1307A-2R7M]	2.74 kOhm [CR2010-FX-2741ELF]
2.7 Ohm [PWR6327N2R70JE]	2.7 uF [MDK15275K100B53P3TUBE]	2.7 uH [SRN4018-2R7M]	2.74 kOhm [CR2010-FX-2741ELF]
2.7 uF [C0805C275K8PACTU]	2.7 uF [MDK15275K50B53P3TUBE]	2.7 uH [SRP1205-2R5Y]	2.74 kOhm [CRT0603-BX-2741ELF]
2.7 uF [C1206C275K3PACTU]	2.7 uF [MDK15275K50B53P3TUBE]	2.7 uH [SRP1250-2R7M]	2.74 kOhm [CRT0603-BY-2741ELF]
2.7 uF [C1206C275K4PACTU]	2.7 uF [MDS15275K50B53P3TUBE]	2.7 uH [SRR0906-2R7ML]	2.8 kOhm [CR0402-FX-2801GLF]
2.7 uF [C1206C275K4PACTU]	2.7 uH [SDE0604A-2R7M]	2.7 uH [SRR0908-2R7ML]	2.8 kOhm [CR0603-FX-2801ELF]
2.7 uF [C1206C275K4RACTU]	2.7 uH [SDR0302-2R7ML]	2.7 uH [SRR1305-2R7ZL]	2.8 kOhm [CR0805-FX-2801ELF]
2.7 uF [C1206C275K8RACTU]	2.7 uH [SDR0403-2R7ML]	2.7 uH [SRR4018-2R7Y]	2.8 kOhm [CR0805-FX-2801ELF]
2.7 uF [C1206C275K9PACTU]	2.7 uH [SDR0604-2R7ML]	2.7 uH [SRR4028-2R7Y]	2.8 kOhm [CR1206-FX-2801ELF]
2.7 uF [C1206C275K9PACTU]	2.7 uH [SDR0703-2R7ML]	2.7 uH [SRR7045-2R7M]	2.8 kOhm [CRT0402-BY-2801GLF]
2.7 uF [C1206C275K9RACTU]	2.7 uH [SDR0906-2R7ML]	2.7 uH [SRU6011-2R7Y]	2.8 kOhm [CRT0805-BX-2801ELF]
		2.74 kOhm [CR0402-FX-2741GLF]	

Multisim 14.1 Base Edition Components

2.8 kOhm [CRT0805-BY- 2801ELF]	2.94 kOhm [CR0805-FX- 2941ELF]	20 kOhm [4306R- 101-203]	20 kOhm [4310R- 101-203LF]
2.8 Ohm [PWR6327N2R80FE]	2.94 kOhm [CR1206-FX- 2941ELF]	20 kOhm [4306R- 101-203LF]	20 kOhm [4310R- 102-203]
2.87 kOhm [CR0402-FX- 2871GLF]	2_AMP 20 kOhm [4108R-1- 203]	20 kOhm [4306R- 102-203]	20 kOhm [4310R- 102-203LF]
2.87 kOhm [CR0603-FX- 2871ELF]	20 kOhm [4108R-1- 203LF]	20 kOhm [4308M- 102-203]	20 kOhm [4416P-1- 203]
2.87 kOhm [CR0805-FX- 2871ELF]	20 kOhm [4114R-1- 203]	20 kOhm [4308M- 102-203LF]	20 kOhm [4416P-1- 203LF]
2.87 kOhm [CR1206-FX- 2871ELF]	20 kOhm [4114R-1- 203LF]	20 kOhm [4308R- 101-203]	20 kOhm [4416P-2- 203]
2.87 kOhm [CR0402-FZ- 2871GLF]	20 kOhm [4114R-2- 203]	20 kOhm [4308R- 102-203]	20 kOhm [4416P-2- 203LF]
2.87 kOhm [CRT0805-BY- 2871ELF]	20 kOhm [4114R-2- 203LF]	20 kOhm [4308R- 101-203LF]	20 kOhm [4416P- T01-203]
2.9 kOhm [4308M- 102-292]	20 kOhm [4114R-2- 203LF]	20 kOhm [4308R- 102-203]	20 kOhm [4416P- T02-203]
2.9 kOhm [4308M- 102-292LF]	20 kOhm [4116R-1- 203]	20 kOhm [4308R- 102-203LF]	20 kOhm [4420P-2- 203]
2.94 kOhm [CR0402-FX- 2941GLF]	20 kOhm [4116R-1- 203LF]	20 kOhm [4309R- 101-203]	20 kOhm [4420P-2- 203LF]
2.94 kOhm [CR0603-FX- 2941ELF]	20 kOhm [4306M- 101-203]	20 kOhm [4309R- 101-203LF]	20 kOhm [4420P- T02-203]
	20 kOhm [4306M- 101-203LF]	20 kOhm [4310M- 101-203]	20 kOhm [4604X- 101-203LF]
		20 kOhm [4310M- 101-203LF]	20 kOhm [4604X- 102-203LF]
		20 kOhm [4310R- 101-203]	20 kOhm [4605X- 101-203LF]

Multisim 14.1 Base Edition Components

20 kOhm [4606H-102-203LF]	20 kOhm [4610H-101-203LF]	20 kOhm [4816P-1-203F]	20 kOhm [4820P-T01-203]
20 kOhm [4606X-101-203LF]	20 kOhm [4610X-101-203LF]	20 kOhm [4816P-1-203LF]	20 kOhm [4820P-T02-203]
20 kOhm [4606X-102-203LF]	20 kOhm [4610X-102-203LF]	20 kOhm [4816P-2-203]	20 kOhm [CAT10-203J4LF]
20 kOhm [4606X-AP1-203LF]	20 kOhm [4610X-AP1-203LF]	20 kOhm [4816P-2-203D]	20 kOhm [CAT16-2002F4LF]
20 kOhm [4606X-AP2-203LF]	20 kOhm [4610X-AP2-203LF]	20 kOhm [4816P-2-203LF]	20 kOhm [CAT16-2002F8LF]
20 kOhm [4607X-101-203LF]	20 kOhm [4612X-102-203LF]	20 kOhm [4816P-T01-203]	20 kOhm [CAT16-203J4LF]
20 kOhm [4608H-101-203LF]	20 kOhm [4814P-1-203]	20 kOhm [4816P-T01-203LF]	20 kOhm [CAT16-203J8LF]
20 kOhm [4608M-102-203LF]	20 kOhm [4814P-1-203LF]	20 kOhm [4816P-T02-203]	20 kOhm [CAT25-203JALF]
20 kOhm [4608X-101-203LF]	20 kOhm [4814P-2-203]	20 kOhm [4816P-T02-203LF]	20 kOhm [CAY10-203J4LF]
20 kOhm [4608X-102-203LF]	20 kOhm [4814P-2-203LF]	20 kOhm [4818P-2-203]	20 kOhm [CAY16-2002F4LF]
20 kOhm [4608X-AP1-203LF]	20 kOhm [4814P-T01-203]	20 kOhm [4818P-T02-203]	20 kOhm [CAY16-203J4LF]
20 kOhm [4608X-AP2-203LF]	20 kOhm [4814P-T01-203LF]	20 kOhm [4820P-1-203]	20 kOhm [CAY16-203J8LF]
20 kOhm [4609M-101-203LF]	20 kOhm [4814P-T02-203]	20 kOhm [4820P-1-203F]	20 kOhm [CAY17-203JALF]
20 kOhm [4609X-101-203LF]	20 kOhm [4814P-T02-203LF]	20 kOhm [4820P-1-203LF]	20 kOhm [CR0201-FW-2002GLF]
20 kOhm [4609X-AP1-203LF]	20 kOhm [4816P-1-203]	20 kOhm [4820P-2-203]	20 kOhm [CR0402-FX-2002GLF]

Multisim 14.1 Base Edition Components

20 kOhm [CR0402-JW-203GLF]	20 kOhm [CRM2512-JW-203ELF]	20 kOhm [CRT1206-BY-2002ELF]	20 mOhm [CRF2512-JZ-R020ELF]
20 kOhm [CR0603-FX-2002ELF]	20 kOhm [CRT0402-BX-2002GLF]	20 kOhm [CRT1206-PV-2002ELF]	20 mOhm [CRL1206-FU-R020ELF]
20 kOhm [CR0603-FX-2002HLF]	20 kOhm [CRT0402-BY-2002GLF]	20 kOhm [PWR220T-20-2002J]	20 mOhm [CRL1206-JU-R020ELF]
20 kOhm [CR0603-JW-203GLF]	20 kOhm [CRT0402-DZ-2002GAS]	20 kOhm [PWR220T-35-2002J]	20 mOhm [CRL2010-FU-R020ELF]
20 kOhm [CR0805-FX-2002ELF]	20 kOhm [CRT0402-FZ-2002GLF]	20 kOhm [PWR221T-30-2002F]	20 mOhm [CRL2512-FU-R020ELF]
20 kOhm [CR0805-JW-203GLF]	20 kOhm [CRT0603-BW-2002ELF]	20 kOhm [PWR263S-35-2002F]	20 mOhm [PWR163S-25-R020J]
20 kOhm [CR1206-FX-2002ELF]	20 kOhm [CRT0603-BY-2002ELF]	20 mOhm [CRA2512-FZ-R020ELF]	20 mOhm [PWR163S-25-R020JE]
20 kOhm [CR1206-JW-203ELF]	20 kOhm [CRT0603-FY-2002ELF]	20 mOhm [CRA2512-JZ-R020ELF]	20 mOhm [PWR1913WR020F]
20 kOhm [CR2512-JW-203ELF]	20 kOhm [CRT0805-BY-2002ELF]	20 mOhm [CRF0805-FX-R020ELF]	20 mOhm [PWR1913WR020F E]
20 kOhm [CRM1206-FX-2002ELF]	20 kOhm [CRT0805-DY-2002ELF]	20 mOhm [CRF1206-FZ-R020ELF]	20 mOhm [PWR1913WR020J]
20 kOhm [CRM2512-FX-2002ELF]	20 kOhm [CRT0805-DZ-2002ELF]	20 mOhm [CRF2512-FZ-R020ELF]	20 mOhm [PWR1913WR020JE]]
			20 mOhm [PWR220T-20-R020J]

Multisim 14.1 Base Edition Components

20 mOhm [PWR220T-35- R020J]	20 mOhm [PWR4525WR020JE]	20 Ohm [CR0603- FX-20R0ELF]	20 Ohm [CRT0805- BY-20R0ELF]
20 mOhm [PWR221T-30- R020J]	20 mOhm [PWR6327WR020J]	20 Ohm [CR0603- JW-200ELF]	20 Ohm [CRT1206- BY-20R0ELF]
20 mOhm [PWR2615WR020F]	20 mOhm [PWR6327WR020JE]	20 Ohm [CR0805- FX-20R0ELF]	20 Ohm [FW20A20R0JA]
20 mOhm [PWR2615WR020F E]	20 Ohm [4114R-1- 200]	20 Ohm [CR0805- JW-200ELF]	20 Ohm [PWR163S-25- 20R0F]
20 mOhm [PWR2615WR020J]	20 Ohm [4114R-1- 200LF]	20 Ohm [CR1206- FX-20R0ELF]	20 Ohm [PWR163S-25- 20R0J]
20 mOhm [PWR2615WR020JE]	20 Ohm [4310R- 101-200]	20 Ohm [CR1206- JW-200ELF]	20 Ohm [PWR163S-25- 20R0JE]
20 mOhm [PWR263S-35- R020J]	20 Ohm [4818P-2- 200]	20 Ohm [CR2010- FX-20R0ELF]	20 Ohm [PWR220T-20- 20R0F]
20 mOhm [PWR4412- 2SBR0200F]	20 Ohm [CAT10- 200J4LF]	20 Ohm [CR2512- FX-20R0ELF]	20 Ohm [PWR220T-20- 20R0J]
20 mOhm [PWR4412- 2SBR0200J]	20 Ohm [CAT16- 20R0F4LF]	20 Ohm [CRM1206-FX- 20R0ELF]	20 Ohm [PWR220T-35- 20R0F]
20 mOhm [PWR4412- 2SCR0200F]	20 Ohm [CAY10- 200J4LF]	20 Ohm [CRM2010-FX- 20R0ELF]	20 Ohm [PWR221T-30- 20R0F]
20 mOhm [PWR4412- 2SDR0200F]	20 Ohm [CAY16- 200J8LF]	20 Ohm [CRM2512-FX- 20R0ELF]	20 Ohm [PWR221T-30- 20R0J]
20 mOhm [PWR4525WR020J]	20 Ohm [CR0402- FX-20R0GLF]	20 Ohm [CRM2512-JW- 200ELF]	20 Ohm [PWR263S-20- 20R0F]
	20 Ohm [CR0402- JW-200GLF]	20 Ohm [CRT0805- BW-20R0ELF]	

Multisim 14.1 Base Edition Components

20 Ohm [PWR263S-20-20R0FE]	20 pF [C0402C200K8GACTU]	20 pF [C1206C200KCGACTU]	20.5 kOhm [CRT0402-FZ-2052GLF]
20 Ohm [PWR263S-20-20R0J]	20 pF [C0603C200K2GACTU]	20 pF [C1210C200KBGACTU]	20.5 kOhm [CRT0805-CX-2052ELF]
20 Ohm [PWR263S-35-20R0F]	20 pF [C0603C200K4GACTU]	20 pF [C1812C200KBGACTU]	20.5 Ohm [CR0402-FX-20R5GLF]
20 Ohm [PWR263S-35-20R0FE]	20 pF [C0603C200K5GACTU]	20 pF [C1825C200KBGACTU]	20.5 Ohm [CR0603-FX-20R5ELF]
20 Ohm [PWR263S-35-20R0J]	20 pF [C0805C200K1GACTU]	20 pF [C2220C200KBGACTU]	20.5 Ohm [CR1206-FX-20R5ELF]
20 Ohm [PWR3014W20R0FE]	20 pF [C0805C200K2GACTU]	20 pF [C2225C200KBGACTU]	20.5 Ohm [CRT0402-FZ-20R5GLF]
20 Ohm [PWR3014W20R0JE]	20 pF [C0805C200K5GACTU]	20.5 kOhm [CR0402-FX-2052GLF]	20_AMP
20 Ohm [PWR4318W20R0JE]	20 pF [C0805C200KBGACTU]	20.5 kOhm [CR0603-FX-2052ELF]	200 kOhm [4114R-1-204]
20 Ohm [PWR4525W20R0F]	20 pF [C1206C200K1GACTU]	20.5 kOhm [CR0805-FX-2052ELF]	200 kOhm [4116R-1-204]
20 Ohm [PWR4525W20R0J]	20 pF [C1206C200K5GACTU]	20.5 kOhm [CR1206-FX-2052ELF]	200 kOhm [4116R-1-204LF]
20 Ohm [PWR5322W20R0JE]	20 pF [C1206C200KBGACTU]	20.5 kOhm [CRT0402-BY-2052GLF]	200 kOhm [4306R-102-204]
20 pF [C0402C200K5GACTU]			200 kOhm [4308R-102-204]
			200 kOhm [4308R-102-204LF]

Multisim 14.1 Base Edition Components

200 kOhm [4606X-101-204LF]	200 kOhm [CR0402-FX-2003GLF]	200 kOhm [CRT0603-AZ-2003ELF]	200 mOhm [CRL2010-FW-R200ELF]
200 kOhm [4606X-102-204LF]	200 kOhm [CR0402-JW-204GLF]	200 kOhm [CRT0603-BY-2003ELF]	200 mOhm [CRL2010-JW-R200ELF]
200 kOhm [4608X-101-204LF]	200 kOhm [CR0603-FX-2003ELF]	200 kOhm [CRT0603-FY-2003ELF]	200 mOhm [CRL2512-FW-R200ELF]
200 kOhm [4610M-102-204LF]	200 kOhm [CR0603-JW-204ELF]	200 kOhm [CRT0805-BY-2003ELF]	200 mOhm [CRM1206-FX-R200ELF]
200 kOhm [4610X-101-204LF]	200 kOhm [CR0805-FX-2003ELF]	200 kOhm [CRT0805-DZ-2003ELF]	200 mOhm [CRM2010-FX-R200ELF]
200 kOhm [4814P-1-204]	200 kOhm [CR0805-JW-204ELF]	200 mOhm [CRL0603-FW-R200ELF]	200 mOhm [CRM2512-FX-R200ELF]
200 kOhm [4814P-2-204]	200 kOhm [CR1206-FX-2003ELF]	200 mOhm [CRL0603-JW-R200ELF]	200 mOhm [CRM2512-JX-R200ELF]
200 kOhm [4814P-2-204LF]	200 kOhm [CR1206-JW-204ELF]	200 mOhm [CRL0805-FW-R200ELF]	200 mOhm [PWR163S-25-R200F]
200 kOhm [CAT16-2003F4LF]	200 kOhm [CRM2010-FX-2003ELF]	200 mOhm [CRL0805-JW-R200ELF]	200 mOhm [PWR163S-25-R200FE]
200 kOhm [CAY16-2003F4LF]	200 kOhm [CRM2512-FX-2003ELF]	200 mOhm [CRL1206-FW-R200ELF]	200 mOhm [PWR163S-25-R200J]
200 kOhm [CAY16-204J4LF]	200 kOhm [CRT0402-BY-2003GLF]	200 mOhm [CRL1206-JW-R200ELF]	200 mOhm [PWR163S-25-R200JE]

Multisim 14.1 Base Edition Components

200 mOhm [PWR1913WR200J]	200 mOhm [PWR263S-35- R200JE]	200 nH [SRP1040- R20M]	200 Ohm [4310R- 102-201LF]
200 mOhm [PWR1913WR200JE]	200 mOhm [PWR3014WR200JE]	200 nH [SRP5015TA-R20Y]	200 Ohm [4420P-1- 201LF]
200 mOhm [PWR220T-20- R200F]	200 mOhm [PWR4318WR200JE]	200 nH [SRP7030- R20FM]	200 Ohm [4420P- T02-201]
200 mOhm [PWR220T-20- R200J]	200 mOhm [PWR4525NR200J]	200 Ohm [4108R-1- 201LF]	200 Ohm [4420P- T02-201LF]
200 mOhm [PWR220T-35- R200F]	200 mOhm [PWR4525NR200JE]	200 Ohm [4114R-1- 201]	200 Ohm [4605X- 101-201LF]
200 mOhm [PWR221T-30- R200F]	200 mOhm [PWR4525WR200F]	200 Ohm [4114R-1- 201LF]	200 Ohm [4606X- 101-201LF]
200 mOhm [PWR2615NR200J]	200 mOhm [PWR4525WR200F E]	200 Ohm [4114R-2- 201]	200 Ohm [4606X- 102-201LF]
200 mOhm [PWR2615NR200JE]	200 mOhm [PWR4525WR200J]	200 Ohm [4116R-1- 201]	200 Ohm [4608X- 101-201LF]
200 mOhm [PWR2615WR200J]	200 mOhm [PWR4525WR200JE]	200 Ohm [4116R-1- 201LF]	200 Ohm [4608X- 102-201LF]
200 mOhm [PWR2615WR200JE]	200 mOhm [PWR6327NR200J]	200 Ohm [4306R- 101-201]	200 Ohm [4608X- AP2-201LF]
200 mOhm [PWR263S-35- R200F]	200 mOhm [PWR6327NR200JE]	200 Ohm [4306R- 101-201LF]	200 Ohm [4609X- 101-201LF]
200 mOhm [PWR263S-35- R200FE]	200 mOhm [PWR6327WR200J]	200 Ohm [4308R- 102-201]	200 Ohm [4610X- 101-201LF]
	200 mOhm [PWR6327WR200JE]	200 Ohm [4308R- 102-201LF]	200 Ohm [4610X- 102-201LF]
		200 Ohm [4310R- 101-201]	200 Ohm [4610X- AP1-201LF]
		200 Ohm [4310R- 101-201LF]	200 Ohm [4816P-1- 201]

Multisim 14.1 Base Edition Components

200 Ohm [4816P-1-201LF]	200 Ohm [CR0201-FW-2000GLF]	200 Ohm [CRM1206-FX-2000ELF]	200 Ohm [PWR263S-35-2000F]
200 Ohm [4816P-2-201]	200 Ohm [CR0201-JW-201GLF]	200 Ohm [CRM2512-FX-2000ELF]	200 Ohm [PWR263S-35-2000FE]
200 Ohm [4816P-2-201LF]	200 Ohm [CR0402-FX-2000GLF]	200 Ohm [CRM2512-JW-201ELF]	200 Ohm [PWR263S-35-2000J]
200 Ohm [4816P-T01-201]	200 Ohm [CR0402-JW-201GLF]	200 Ohm [CRT0603-FX-2000ELF]	200 Ohm [PWR4525W2000F]
200 Ohm [4816P-T01-201LF]	200 Ohm [CR0603-FX-2000GLF]	200 Ohm [CRT0805-BY-2000ELF]	200 pF [C0402C201K1HACT U]
200 Ohm [4816P-T02-201]	200 Ohm [CR0603-JW-201ELF]	200 Ohm [CRT0805-FV-2000ELF]	200 pF [C0402C201K3HACT U]
200 Ohm [4816P-T02-201LF]	200 Ohm [CR0603-JW-201GLF]	200 Ohm [PWR163S-25-2000FE]	200 pF [C0402C201K5HACT U]
200 Ohm [CAT16-2000F4LF]	200 Ohm [CR0805-FX-2000ELF]	200 Ohm [PWR220T-35-2000F]	200 pF [C0603C201K5GACT U]
200 Ohm [CAT16-201J4LF]	200 Ohm [CR0805-JW-201ELF]	200 Ohm [PWR221T-30-2000F]	200 pF [C0805C201K2GACT U]
200 Ohm [CAT16-201J8LF]	200 Ohm [CR1206-FX-2000ELF]	200 Ohm [PWR263S-20-2000F]	200 pF [C0805C201K5GACT U]
200 Ohm [CAT25-201JALF]	200 Ohm [CR1206-JW-201GLF]	200 Ohm [PWR263S-20-2000J]	200 pF [C1206C201K5GACT U]
200 Ohm [CAY10-201J4LF]	200 Ohm [CR2010-JW-201ELF]		
200 Ohm [CAY16-2000F4LF]	200 Ohm [CR2512-JW-201ELF]		
200 Ohm [CAY16-201J4LF]			
200 Ohm [CAY16-201J8LF]			

Multisim 14.1 Base Edition Components

200 pF [C1206C201KBGAC TU]	205 Ohm [CR1206- FX-2050ELF]	21.5 kOhm [CR0402-FX- 2152GLF]	21.5 Ohm [CRT0402-FZ- 21R5GLF]
200 pF [C1210C201KBGAC TU]	205 Ohm [CRT0402-FZ- 2050GLF]	21.5 kOhm [CR0603-FX- 2152ELF]	210 kOhm [CR0402-FX- 2103GLF]
200 pF [C1812C201KBGAC TU]	21 kOhm [CR0402- FX-2102GLF]	21.5 kOhm [CR0603-FX- 2152GLF]	210 kOhm [CR0603-FX- 2103ELF]
200 pF [C2220C201KBGAC TU]	21 kOhm [CR0805- FX-2102ELF]	21.5 kOhm [CR0805-FX- 2152ELF]	210 kOhm [CR0805-FX- 2103ELF]
200 pF [C2225C201KBGAC TU]	21 kOhm [CR1206- FX-2102ELF]	21.5 kOhm [CR1206-FX- 2152ELF]	210 kOhm [CR1206-FX- 2103ELF]
200 uH [SDR1105- 201KL]	21 kOhm [CRT0603-BY- 2102ELF]	21.5 kOhm [CRT0402-FZ- 2152GLF]	210 kOhm [CRT0805-BY- 2103ELF]
2013655-1	21 Ohm [CR0402- FX-21R0GLF]	21.5 kOhm [CRT0603-BY- 2152ELF]	210 Ohm [4816P-1- 211]
205 kOhm [CR0603-FX- 2053ELF]	21 Ohm [CR0603- FX-21R0ELF]	21.5 kOhm [CRT0603-FZ- 2152ELF]	210 Ohm [4816P-1- 211LF]
205 kOhm [CR0805-FX- 2053ELF]	21 Ohm [CR0805- FX-21R0ELF]	21.5 kOhm [CRT0805-DZ- 2152ELF]	210 Ohm [CR0402- FX-2100GLF]
205 kOhm [CR1206-FX- 2053ELF]	21 Ohm [PWR2615W21R0F]	21.5 Ohm [CR0603- FX-21R5ELF]	210 Ohm [CR0603- FX-2100ELF]
205 Ohm [CR0402- FX-2050GLF]	21 Ohm [PWR2615W21R0J]	21.5 Ohm [CR0805- FX-21R5ELF]	210 Ohm [CR0805- FX-2100ELF]
205 Ohm [CR0603- FX-2050ELF]	21.5 kOhm [CAT16- 2152F4LF]	21.5 Ohm [CR1206- FX-21R5ELF]	215 kOhm [CR0402-FX- 2153GLF]
205 Ohm [CR0805- FX-2050ELF]	21.5 kOhm [CAY16- 2152F4LF]		

Multisim 14.1 Base Edition Components

215 kOhm [CR0603-FX- 2153ELF]	22 kOhm [4116R-1- 223LF]	22 kOhm [4308M- 101-223]	22 kOhm [4310R- 102-223]
215 kOhm [CR0805-FX- 2153ELF]	22 kOhm [4116R-2- 223]	22 kOhm [4308M- 101-223LF]	22 kOhm [4310R- 102-223LF]
215 kOhm [CR1206-FX- 2153ELF]	22 kOhm [4116R-2- 223LF]	22 kOhm [4308M- 102-223]	22 kOhm [4311R- 101-223LF]
215 Ohm [CR0402- FX-2150GLF]	22 kOhm [4304M- 101-223]	22 kOhm [4308M- 102-223LF]	22 kOhm [4416P-1- 223]
215 Ohm [CR0603- FX-2150ELF]	22 kOhm [4306H- 102-223]	22 kOhm [4308R- 101-223]	22 kOhm [4416P-2- 223]
215 Ohm [CR0805- FX-2150ELF]	22 kOhm [4306H- 102-223LF]	22 kOhm [4308R- 101-223LF]	22 kOhm [4416P- T02-223]
215 Ohm [CR1206- FX-2150ELF]	22 kOhm [4306M- 101-223]	22 kOhm [4308R- 102-223]	22 kOhm [4420P-2- 223]
215 Ohm [CRT0402-FZ- 2150GLF]	22 kOhm [4306M- 101-223LF]	22 kOhm [4308R- 102-223LF]	22 kOhm [4420P-2- 223LF]
22 kOhm [4108R-1- 223LF]	22 kOhm [4306R- 101-223]	22 kOhm [4309R- 101-223]	22 kOhm [4420P- T02-223]
22 kOhm [4114R-1- 223]	22 kOhm [4306R- 101-223LF]	22 kOhm [4309R- 101-223LF]	22 kOhm [4420P- T02-223LF]
22 kOhm [4114R-1- 223LF]	22 kOhm [4306R- 102-223]	22 kOhm [4310H- 101-223]	22 kOhm [4604X- 101-223LF]
22 kOhm [4114R-2- 223]	22 kOhm [4306R- 102-223LF]	22 kOhm [4310H- 101-223LF]	22 kOhm [4604X- 102-223LF]
22 kOhm [4114R-2- 223LF]	22 kOhm [4308H- 101-223]	22 kOhm [4310M- 101-223]	22 kOhm [4604X- AP2-223LF]
22 kOhm [4116R-1- 223]	22 kOhm [4308H- 102-223]	22 kOhm [4310R- 101-223]	22 kOhm [4605X- 101-223LF]
	22 kOhm [4308H- 102-223LF]	22 kOhm [4310R- 101-223LF]	22 kOhm [4605X- AP1-223LF]

Multisim 14.1 Base Edition Components

22 kOhm [4606H-101-223LF]	22 kOhm [4610H-101-223LF]	22 kOhm [4814P-T01-223LF]	22 kOhm [4820P-2-223]
22 kOhm [4606M-101-223LF]	22 kOhm [4610H-102-223LF]	22 kOhm [4814P-T02-223]	22 kOhm [4820P-2-223F]
22 kOhm [4606X-101-223LF]	22 kOhm [4610M-101-223LF]	22 kOhm [4814P-T02-223LF]	22 kOhm [4820P-2-223LF]
22 kOhm [4606X-102-223LF]	22 kOhm [4610X-101-223LF]	22 kOhm [4816P-1-223]	22 kOhm [4820P-T01-223]
22 kOhm [4606X-AP1-223LF]	22 kOhm [4610X-102-223LF]	22 kOhm [4816P-1-223DLF]	22 kOhm [4820P-T02-223]
22 kOhm [4607X-101-223LF]	22 kOhm [4610X-AP1-223LF]	22 kOhm [4816P-1-223LF]	22 kOhm [CAT10-223J4LF]
22 kOhm [4608H-102-223LF]	22 kOhm [4611X-101-223LF]	22 kOhm [4816P-2-223]	22 kOhm [CAT16-2202F4LF]
22 kOhm [4608X-101-223LF]	22 kOhm [4612X-102-223LF]	22 kOhm [4816P-2-223LF]	22 kOhm [CAT16-223J2LF]
22 kOhm [4608X-102-223LF]	22 kOhm [4613X-101-223LF]	22 kOhm [4816P-T01-223]	22 kOhm [CAT16-223J4LF]
22 kOhm [4608X-AP1-223LF]	22 kOhm [4614X-102-223LF]	22 kOhm [4816P-T01-223LF]	22 kOhm [CAT16-223J8LF]
22 kOhm [4608X-AP2-223LF]	22 kOhm [4814P-1-223]	22 kOhm [4816P-T02-223]	22 kOhm [CAT25-223JALF]
22 kOhm [4609H-101-223LF]	22 kOhm [4814P-1-223LF]	22 kOhm [4816P-T02-223LF]	22 kOhm [CAY10-223J4LF]
22 kOhm [4609M-101-223LF]	22 kOhm [4814P-2-223]	22 kOhm [4818P-T02-223]	22 kOhm [CAY16-2202F4LF]
22 kOhm [4609X-101-223LF]	22 kOhm [4814P-2-223LF]	22 kOhm [4820P-1-223]	22 kOhm [CAY16-223J4GLF]
22 kOhm [4609X-AP1-223LF]	22 kOhm [4814P-T01-223]	22 kOhm [4820P-1-223LF]	22 kOhm [CAY16-223J4LF]

Multisim 14.1 Base Edition Components

22 kOhm [CAY16-223J8LF]	22 kOhm [CR2512-JW-223ELF]	22 nF [0306ZC223KAT2A]	22 nF [C0402C223K9RACTU]
22 kOhm [CAY17-223JALF]	22 kOhm [CRM1206-FX-2202ELF]	22 nF [05083C223KAT2S]	22 nF [C0603C223K1RACTU]
22 kOhm [CR0201-JW-223GLF]	22 kOhm [CRM1206-JW-223ELF]	22 nF [05085C223KAT2V]	22 nF [C0603C223K3RACTU]
22 kOhm [CR0402-FX-2202GLF]	22 kOhm [CRM2512-JW-223ELF]	22 nF [06125C223KAT2W]	22 nF [C0603C223K4RACTU]
22 kOhm [CR0402-JW-223GLF]	22 kOhm [CRT0402-BY-2202GLF]	22 nF [0612ZC223KAT2S]	22 nF [C0603C223K5RACTU]
22 kOhm [CR0603-FX-2202ELF]	22 kOhm [CRT0603-PW-2202ELF]	22 nF [C0402C223K3RACTU]	22 nF [C0603C223K8RACTU]
22 kOhm [CR0603-JW-223ELF]	22 kOhm [CRT0805-BY-2202ELF]	22 nF [C0402C223K4RACTU]	22 nF [C0603C223M3VAC TU]
22 kOhm [CR0805-FX-2202ELF]	22 kOhm [CRT1206-BY-2202ELF]	22 nF [C0402C223K5RACTU]	22 nF [C0603C223M8VAC TU]
22 kOhm [CR0805-JW-223ELF]	22 kOhm [PWR6327W2202J]	22 nF [C0402C223K8PACTU]	22 nF [C0805C223K1RACTU]
22 kOhm [CR1206-FX-2202ELF]	22 kOhm [PWR6327W2202JE]	22 nF [C0402C223K8RACTU]	22 nF [C0805C223K2RACTU]
22 kOhm [CR1206-JW-223GLF]	22 nF [03063C223KAT2A]	22 nF [C0402C223K9PACTU]	22 nF [C0805C223K3GACTU]
22 kOhm [CR2010-JW-223ELF]	22 nF [0306YC223KAT2A]		

Multisim 14.1 Base Edition Components

22 nF [C0805C223K3HACT U]	22 nF [C0805F223K5RACT U]	22 nF [C1206F223K2RACT U]	22 nF [C1812C223K1GACT U]
22 nF [C0805C223K3RACT U]	22 nF [C1206C223K1HACT U]	22 nF [C1210C223K1GACT U]	22 nF [C1812C223K1HACT U]
22 nF [C0805C223K4RACT U]	22 nF [C1206C223K1RACT U]	22 nF [C1210C223K1HACT U]	22 nF [C1812C223K1RACT U]
22 nF [C0805C223K5HACT U]	22 nF [C1206C223K2RACT U]	22 nF [C1210C223K1RACT U]	22 nF [C1812C223K2RACT U]
22 nF [C0805C223K5RACT U]	22 nF [C1206C223K3GACT U]	22 nF [C1210C223K2RACT U]	22 nF [C1812C223K5GACT U]
22 nF [C0805C223K8RACT U]	22 nF [C1206C223K3HACT U]	22 nF [C1210C223K3GACT U]	22 nF [C1812C223K5HACT U]
22 nF [C0805C223KARACT U]	22 nF [C1206C223K3RACT U]	22 nF [C1210C223K3HACT U]	22 nF [C1812C223K5RACT U]
22 nF [C0805C223M5UAC TU]	22 nF [C1206C223K4RACT U]	22 nF [C1210C223K5GACT U]	22 nF [C1825C223K1GACT U]
22 nF [C0805F223K1RACT U]	22 nF [C1206C223K5HACT U]	22 nF [C1210C223K5HACT U]	22 nF [C1825C223K5GACT U]
22 nF [C0805F223K3RACT U]	22 nF [C1206C223K5RACT U]	22 nF [C1210C223K5RACT U]	22 nF [C1825C223K5RACT U]
22 nF [C0805F223K4RACT U]	22 nF [C1206C223M5UAC TU]	22 nF [C1210C223KARACT U]	22 nF [C2220C223K1GACT U]

Multisim 14.1 Base Edition Components

22 nF [C2220C223K2GACT U]	22 nF [LG126Z223MAT2S 1]	22 nF [PG224Z223MAB2S 1]	22 Ohm [4108R-1- 220]
22 nF [C2225C223K1GACT U]	22 nF [MMC5.7223K250J 35TR12]	22 nF [PG226D223MAB2S 1]	22 Ohm [4108R-1- 220LF]
22 nF [C2225C223K5GACT U]	22 nF [MMC5.7223K50J3 1TR12]	22 nF [PG226W223MAB2 S1]	22 Ohm [4114R-1- 220]
22 nF [GMC5.7222K250J3 1TR12]	22 nF [PG124D223MAB2S 1]	22 nF [PG226Z223MAB2S 1]	22 Ohm [4114R-2- 220]
22 nF [GMC5.7223K100J3 1TR12]	22 nF [PG124W223MAB2 S1]	22 nF [SMC5.7223K100J3 3TR12]	22 Ohm [4114R-2- 220LF]
22 nF [GMC5.7223K50J31 TR12]	22 nF [PG124Z223MAB2S 1]	22 nF [SPC10.2223K100A 31TR16]	22 Ohm [4116R-1- 220LF]
22 nF [GMC7.3222K250K3 1TR12]	22 nF [PG126D223MAB2S 1]	22 nF [SPC10.2223K250A 31TR16]	22 Ohm [4116R-2- 220]
22 nF [GMC7.3222K63K31 TR12]	22 nF [PG126W223MAB2 S1]	22 nF [SPC10.2223K400A 31TR16]	22 Ohm [4116R-2- 220LF]
22 nF [GMC7.3223K63K31 TR12]	22 nF [PG126Z223MAB2S 1]	22 nF [SPC12.7223K630B 31TR24]	22 Ohm [4304M- 102-220]
22 nF [GPC7.3223K63K31 TR12]	22 nF [PG224D223MAB2S 1]	22 nF [SPC7.3223K100K35 TR12]	22 Ohm [4304M- 102-220LF]
22 nF [LD16YC223KAB2A]	22 nF [PG224W223MAB2 S1]	22 nF [W3F15C2238AT1A]	22 Ohm [4306M- 101-220]
			22 Ohm [4306M- 102-220]
			22 Ohm [4306R- 101-220]

Multisim 14.1 Base Edition Components

22 Ohm [4306R-101-220LF]	22 Ohm [4310R-102-220LF]	22 Ohm [4608X-101-220LF]	22 Ohm [4816P-1-220]
22 Ohm [4306R-102-220]	22 Ohm [4416P-1-220]	22 Ohm [4608X-102-220LF]	22 Ohm [4816P-1-220G]
22 Ohm [4306R-102-220LF]	22 Ohm [4416P-T01-220]	22 Ohm [4608X-AP2-220LF]	22 Ohm [4816P-1-220LF]
22 Ohm [4308H-102-220]	22 Ohm [4420P-1-220]	22 Ohm [4609X-101-220LF]	22 Ohm [4816P-2-220]
22 Ohm [4308M-102-220]	22 Ohm [4420P-1-220LF]	22 Ohm [4610X-101-220LF]	22 Ohm [4816P-2-220LF]
22 Ohm [4308M-102-220LF]	22 Ohm [4420P-T01-220]	22 Ohm [4610X-102-220LF]	22 Ohm [4816P-T01-220]
22 Ohm [4308R-101-220]	22 Ohm [4420P-T04-220]	22 Ohm [4610X-AP2-220LF]	22 Ohm [4816P-T01-220LF]
22 Ohm [4308R-101-220LF]	22 Ohm [4604X-101-220LF]	22 Ohm [4612X-102-220LF]	22 Ohm [4816P-T02-220]
22 Ohm [4308R-102-220]	22 Ohm [4604X-102-220LF]	22 Ohm [4614X-102-220LF]	22 Ohm [4816P-T02-220LF]
22 Ohm [4308R-102-220LF]	22 Ohm [4605X-101-220LF]	22 Ohm [4814P-1-220]	22 Ohm [4818P-T01-220]
22 Ohm [4309R-101-220]	22 Ohm [4606X-101-220LF]	22 Ohm [4814P-1-220LF]	22 Ohm [4820P-1-220]
22 Ohm [4310M-102-220]	22 Ohm [4606X-102-220LF]	22 Ohm [4814P-2-220]	22 Ohm [4820P-1-220G]
22 Ohm [4310R-101-220]	22 Ohm [4606X-AP2-220LF]	22 Ohm [4814P-T01-220]	22 Ohm [4820P-1-220LF]
22 Ohm [4310R-101-220LF]	22 Ohm [4607X-101-220LF]	22 Ohm [4814P-T01-220LF]	22 Ohm [4820P-T01-220]
22 Ohm [4310R-102-220]	22 Ohm [4608H-102-220LF]	22 Ohm [4814P-T02-220]	22 Ohm [CAT10-220J4LF]

Multisim 14.1 Base Edition Components

22 Ohm [CAT16-220J2GLF]	22 Ohm [CR0201-JW-220GLF]	22 Ohm [CR2512-JW-220ELF]	22 Ohm [PWR220T-20-22R0J]
22 Ohm [CAT16-220J2LF]	22 Ohm [CR0402-FX-22R0GLF]	22 Ohm [CRM0805-JW-220ELF]	22 Ohm [PWR221T-30-22R0F]
22 Ohm [CAT16-220J4GLF]	22 Ohm [CR0402-JW-220GLF]	22 Ohm [CRM1206-FX-22R0ELF]	22 Ohm [PWR2615W22R0F]
22 Ohm [CAT16-220J4LF]	22 Ohm [CR0603-FX-22R0ELF]	22 Ohm [CRM1206-JW-220ELF]	22 Ohm [PWR2615W22R0J]
22 Ohm [CAT16-220J8LF]	22 Ohm [CR0603-FX-22R0HLF]	22 Ohm [CRM2512-JW-220ELF]	22 Ohm [PWR2615W22R0JE]
22 Ohm [CAT16-22R0F4LF]	22 Ohm [CR0603-JW-220ELF]	22 Ohm [CRT0603-FY-22R0ELF]	22 Ohm [PWR4525W22R0J]
22 Ohm [CAT25-220JALF]	22 Ohm [CR0603-JW-220GLF]	22 Ohm [CRT0805-BY-22R0ELF]	22 Ohm [PWR4525W22R0JE]
22 Ohm [CAY10-220J2LF]	22 Ohm [CR0805-FX-22R0ELF]	22 Ohm [FW10A22R0JA]	22 Ohm [PWR6327W22R0F]
22 Ohm [CAY10-220J4LF]	22 Ohm [CR0805-FX-22R0GLF]	22 Ohm [FW20A22R0JA]	22 Ohm [PWR6327W22R0J]
22 Ohm [CAY16-220J2LF]	22 Ohm [CR0805-JW-220ELF]	22 Ohm [FW30A22R0JA]	22 Ohm [PWR6327W22R0JE]
22 Ohm [CAY16-220J4LF]	22 Ohm [CR0805-JW-220GLF]	22 Ohm [FW50A22R0JA]	22 Ohm [W1M22R0J]
22 Ohm [CAY16-220J8LF]	22 Ohm [CR1206-FX-22R0ELF]	22 Ohm [FW70A22R0JA]	22 Ohm [W3M22R0J]
22 Ohm [CAY16-22R0F4LF]	22 Ohm [CR1206-FX-22R0GLF]	22 Ohm [PWR220T-20-22R0F]	22 Ohm [WS2M22R0J]
22 Ohm [CAY17-220JALF]	22 Ohm [CR1206-JW-220ELF]		
22 Ohm [CR0201-FW-22R0GLF]	22 Ohm [CR2010-JW-220ELF]		

Multisim 14.1 Base Edition Components

22 pF [C0201C220K3GACT U]	22 pF [C0805C220K2GACT U]	22 pF [C1206C220KDGAC TU]	22 pF [CA064C220K5GAC TU]
22 pF [C0402C220K3GACT U]	22 pF [C0805C220K3GACT U]	22 pF [C1210C220K2GACT U]	22 pF [CA064C220K8GAC TU]
22 pF [C0402C220K4GACT U]	22 pF [C0805C220K5GACT U]	22 pF [C1210C220K5GACT U]	22 pF [W2F11A2208AT1A]
22 pF [C0402C220K5GACT U]	22 pF [C0805C220KBGAC TU]	22 pF [C1210C220KBGAC TU]	22 pF [W3F11A2208AT1A]
22 pF [C0402C220K8GACT U]	22 pF [C0805C220KCGAC TU]	22 pF [C1812C220KBGAC TU]	22 uF [20SVP22M] 22 uF [20TQC22MYFB]
22 pF [C0603C220K1GACT U]	22 pF [C0805C220KDGAC TU]	22 pF [C1825C220KBGAC TU]	22 uF [25TQC22MV]
22 pF [C0603C220K2GACT U]	22 pF [C1206C220K1GACT U]	22 pF [C2220C220KBGAC TU]	22 uF [25TQC22MYFD]
22 pF [C0603C220K3GACT U]	22 pF [C1206C220K2GACT U]	22 pF [C2225C220KBGAC TU]	22 uF [25TQC22MYFT]
22 pF [C0603C220K4GACT U]	22 pF [C1206C220K5GACT U]	22 pF [CA064C220K2GAC TU]	22 uF [32SEPF22M] 22 uF [35SEPF22M]
22 pF [C0603C220K5GACT U]	22 pF [C1206C220KBGAC TU]	22 pF [CA064C220K3GAC TU]	22 uF [6TPU22MSI] 22 uF [8TPC22M]
22 pF [C0805C220K1GACT U]	22 pF [C1206C220KCGAC TU]	22 pF [CA064C220K4GAC TU]	22 uF [A700D226M016AT E018]
			22 uF [A700V226M006AT E028]

Multisim 14.1 Base Edition Components

22 uF [A700V226M006AT E045]	22 uF [C1210C226K9PACT U]	22 uF [EEHZA1J220XP]	22 uF [T491B226M020AT]
22 uF [A700V226M008AT E028]	22 uF [C1210C226K9RACT U]	22 uF [EEHZA1K220P]	22 uF [T491C226M004AT]
22 uF [A700V226M008AT E045]	22 uF [C1210C226M8VAC TU]	22 uF [EEHZA1V220R]	22 uF [T491C226M006AT]
22 uF [A700V226M010AT E028]	22 uF [EEFCS1C220R]	22 uF [EEHZC1J220XP]	22 uF [T491C226M016AT]
22 uF [A700V226M12RAT E030]	22 uF [EEFCS1D220R]	22 uF [EEHZC1V220R]	22 uF [T491C226M020AT]
22 uF [C0805C226K9PACT U]	22 uF [EEFCT1E220R]	22 uF [T419G226M020AH 4250]	22 uF [T491C226M025AT]
22 uF [C1206C226K9PACT U]	22 uF [EEFCX1C220R]	22 uF [T429D226M006AH 4250]	22 uF [T491D226M010AT]
22 uF [C1206C226M9VAC TU]	22 uF [EEFCX1D220R]	22 uF [T491A226M004AT]	22 uF [T491D226M016AT]
22 uF [C1210C226K4PACT U]	22 uF [EEFCX1E220R]	22 uF [T491A226M006AT]	22 uF [T491D226M020AT]
22 uF [C1210C226K8PACT U]	22 uF [EEFHX1C220R]	22 uF [T491A226M010AT]	22 uF [T491D226M025AT]
22 uF [C1210C226K8PACT U]	22 uF [EEFHX1D220R]	22 uF [T491B226M004AT]	22 uF [T491D226M035AT]
22 uF [C1210C226K8RACT U]	22 uF [EEFHX1E220R]	22 uF [T491B226M006AT]	22 uF [T491D226M035AT]
	22 uF [EEHZA1H220P]	22 uF [T491B226M010AT]	22 uF [T491S226M004AT]
		22 uF [T491B226M016AT]	

Multisim 14.1 Base Edition Components

22 uF [T491T226M004AT]	22 uF [T494B226M004AT]	22 uF [T494D226M025AT]	22 uF [T495C226M025AT E300]
22 uF [T491T226M006AT]	22 uF [T494B226M006AT]	22 uF [T494D226M035AT]	22 uF [T495C226M025AT E900]
22 uF [T491T226M010AT]	22 uF [T494B226M010AT]	22 uF [T494S226M004AT]	22 uF [T495D226M020AT E180]
22 uF [T491U226M006AT]	22 uF [T494B226M016AT]	22 uF [T494T226M004AT]	22 uF [T495D226M020AT E225]
22 uF [T491U226M010AT]	22 uF [T494C226M004AT]	22 uF [T494T226M006AT]	22 uF [T495D226M025AT E200]
22 uF [T491U226M016AT]	22 uF [T494C226M006AT]	22 uF [T494T226M010AT]	22 uF [T495D226M035AT E125]
22 uF [T491V226M020AT]	22 uF [T494C226M010AT]	22 uF [T494U226M006AT]	22 uF [T495D226M035AT E200]
22 uF [T491V226M025AT]	22 uF [T494C226M016AT]	22 uF [T494U226M010AT]	22 uF [T495D226M035AT E300]
22 uF [T491X226M035AT]	22 uF [T494C226M020AT]	22 uF [T494U226M016AT]	22 uF [T495X226M025AT E225]
22 uF [T491X226M050AT]	22 uF [T494D226M010AT]	22 uF [T494V226M020AT]	22 uF [T495X226M035AT E125]
22 uF [T493X226M025AH 6110]	22 uF [T494D226M016AT]	22 uF [T494X226M035AT]	22 uF [T495X226M035AT E200]
22 uF [T494A226M004AT]	22 uF [T494D226M020AT]		
22 uF [T494A226M006AT]			
22 uF [T494A226M010AT]			

Multisim 14.1 Base Edition Components

22 uF [T495X226M035AT E275]	22 uF [T510X226M035AT E100]	22 uF [TACR226K002RTA]	22 uF [TAJC226K025RNJ]
22 uF [T497D226M006AT 6110]	22 uF [T520A226M006AT E090]	22 uF [TACR226K003RTA]	22 uF [TAJD226K016RNJ]
22 uF [T498B226M010AT E1K5]	22 uF [T520A226M006AT E100]	22 uF [TACR226K004RTA]	22 uF [TAJD226K020RNJ]
22 uF [T498C226M006AT E1K3]	22 uF [T520A226M010AT E080]	22 uF [TACR226K006RTA]	22 uF [TAJD226K025RNJ]
22 uF [T498C226M010AT E1K1]	22 uF [T520C226M016AT E080]	22 uF [TAJA226K004RNJ]	22 uF [TAJD226K035RNJ]
22 uF [T498C226M016AT E1K0]	22 uF [T520T226M008AT E070]	22 uF [TAJA226K006RNJ]	22 uF [TAJE226K035RNJ]
22 uF [T498D226M025AT E600]	22 uF [T520V226M020AT E045]	22 uF [TAJA226K010RNJ]	22 uF [TAJP226K004RNJ]
22 uF [T498X226M035AT E500]	22 uF [T520V226M020AT E090]	22 uF [TAJB226K006RNJ]	22 uF [TAJR226K004RNJ]
22 uF [T499D226M016AT E800]	22 uF [T521V226M025AT E060]	22 uF [TAJB226K010RNJ]	22 uF [TAJS226K004RNJ]
22 uF [T510X226M035AT E060]	22 uF [T525B226M010AT E080]	22 uF [TAJB226K016RNJ]	22 uF [TAJS226K006RNJ]
22 uF [T510X226M035AT E080]	22 uF [T541X226M050AH 6510]	22 uF [TAJB226K020RNJ]	22 uF [TAJT226K004RNJ]
		22 uF [TAJC226K006RNJ]	22 uF [TAJT226K006RNJ]
		22 uF [TAJC226K010RNJ]	22 uF [TAJT226K010RNJ]
		22 uF [TAJC226K016RNJ]	22 uF [TAJW226K010RNJ]
		22 uF [TAJC226K020RNJ]	22 uF [TAJW226K016RNJ]

Multisim 14.1 Base Edition Components

22 uF [TAJW226K020RNJ]	22 uF [TPME226K050R01 00]	22 uF [TPSC226K016R030 0]	22 uF [TPSD226K035R020 0]
22 uF [TAJY226K020RNJ]	22 uF [TPSA226K006R050 0]	22 uF [TPSC226K016R037 5]	22 uF [TPSD226K035R030 0]
22 uF [TAJY226K025RNJ]			
22 uF [TAJY226K035RNJ]	22 uF [TPSA226K006R090 0]	22 uF [TPSC226K020R015 0]	22 uF [TPSD226K035R040 0]
22 uF [THJB226K006RJN]	22 uF [TPSB226K006R060 0]	22 uF [TPSC226K020R040 0]	22 uF [TPSE226K035R012 5]
22 uF [THJB226K010RJN]	22 uF [TPSB226K010R040 0]	22 uF [TPSC226K025R040 0]	22 uF [TPSE226K035R020 0]
22 uF [THJC226K016RJN]			
22 uF [THJD226K025RJN]	22 uF [TPSB226K010R050 0]	22 uF [TPSD226K020R020 0]	22 uF [TPSE226K035R030 0]
22 uF [THJD226K035R030 0]	22 uF [TPSB226K010R070 0]	22 uF [TPSD226K020R030 0]	22 uF [TPST226K010R080 0]
22 uF [THJD226K035RJN]	22 uF [TPSB226K016R060 0]	22 uF [TPSD226K025R010 0]	22 uF [TPSW226K016R05 00]
22 uF [TPMD226K035R00 70]	22 uF [TPSC226K010R030 0]	22 uF [TPSD226K025R020 0]	22 uF [TRJA226K006RRJ]
22 uF [TPME226K035R00 60]	22 uF [TPSC226K016R015 0]	22 uF [TPSD226K025R030 0]	22 uF [TRJB226K006RRJ]
22 uF [TPME226K035R01 00]	22 uF [TPSC226K016R025 0]	22 uF [TPSD226K035R012 5]	22 uF [TRJB226K010RRJ]
			22 uF [TRJB226K016RRJ]

Multisim 14.1 Base Edition Components

22 uF [TRJC226K016RRJ]	22 uH [SDR0805- 220ML]	22 uH [SRN3010- 220M]	22 uH [SRP7050TA- 220M]
22 uF [TRJC226K020RRJ]	22 uH [SDR0906- 220ML]	22 uH [SRN3015- 220M]	22 uH [SRR0603- 220ML]
22 uF [TRJD226K035RRJ]	22 uH [SDR1005- 220ML]	22 uH [SRN4012T- 220M]	22 uH [SRR0604- 220ML]
22 uF [TRME226K035R00 60]	22 uH [SDR1006- 220ML]	22 uH [SRN4018- 220M]	22 uH [SRR0618- 220ML]
22 uF [TRME226K035R01 00]	22 uH [SDR1030- 220M]	22 uH [SRN4026- 220M]	22 uH [SRR0735A- 220M]
22 uH [SDE0403A- 220M]	22 uH [SDR1045- 220M]	22 uH [SRN5020- 220M]	22 uH [SRR0745A- 220M]
22 uH [SDE0604A- 220M]	22 uH [SDR1105- 220ML]	22 uH [SRN5040- 220M]	22 uH [SRR0804- 220Y]
22 uH [SDE0805A- 220M]	22 uH [SDR1305- 220M]	22 uH [SRN6028- 220M]	22 uH [SRR0805- 220Y]
22 uH [SDE1006A- 220M]	22 uH [SDR1307- 220ML]	22 uH [SRN6045- 220M]	22 uH [SRR0905- 220M]
22 uH [SDR0302- 220ML]	22 uH [SDR1307A- 220M]	22 uH [SRN8040- 220M]	22 uH [SRR0906- 220ML]
22 uH [SDR0403- 220ML]	22 uH [SDR1806- 220ML]	22 uH [SRP1038A- 220M]	22 uH [SRR0908- 220ML]
22 uH [SDR0503- 220ML]	22 uH [SDR6603- 220M]	22 uH [SRP1265A- 220M]	22 uH [SRR1003- 220M]
22 uH [SDR0603- 220ML]	22 uH [SDR7030- 220M]	22 uH [SRP1770TA- 220M]	22 uH [SRR1005- 220Y]
22 uH [SDR0604- 220YL]	22 uH [SDR7045- 220M]	22 uH [SRP5015TA- 220M]	22 uH [SRR1205- 220ML]
22 uH [SDR0703- 220KL]	22 uH [SRN1060- 220M]	22 uH [SRP6540- 220M]	22 uH [SRR1206- 220ML]

Multisim 14.1 Base Edition Components

22 uH [SRR1208-220ML]	22 uH [SRR6038-220Y]	22 uH [SRU2016-220Y]	22 uH [SRU8028A-220Y]
22 uH [SRR1210-220M]	22 uH [SRR6040A-220M]	22 uH [SRU3014-220Y]	22 uH [SRU8043-220Y]
22 uH [SRR1210A-220M]	22 uH [SRR6603-220ML]	22 uH [SRU3017-220Y]	22.1 kOhm [CAT16-2212F4LF]
22 uH [SRR1240-220M]	22 uH [SRR7032-220M]	22 uH [SRU3028-220Y]	22.1 kOhm [CAY16-2212F4LF]
22 uH [SRR1260-220M]	22 uH [SRR7045-220M]	22 uH [SRU3028A-220Y]	22.1 kOhm [CR0402-FX-2212GLF]
22 uH [SRR1260A-220M]	22 uH [SRU1028-220Y]	22 uH [SRU5011-220Y]	22.1 kOhm [CR0603-FX-2212ELF]
22 uH [SRR1280-220M]	22 uH [SRU1028A-220Y]	22 uH [SRU5016-220Y]	22.1 kOhm [CR0805-FX-2212ELF]
22 uH [SRR1806-220M]	22 uH [SRU1038-220Y]	22 uH [SRU5018-220Y]	22.1 kOhm [CR1206-FX-2212ELF]
22 uH [SRR3011-220YL]	22 uH [SRU1038A-220Y]	22 uH [SRU5028-220Y]	22.1 kOhm [CR1206-FX-2212GLF]
22 uH [SRR4011-220YL]	22 uH [SRU1048-220Y]	22 uH [SRU5028A-220Y]	22.1 kOhm [CRT0603-BY-2212ELF]
22 uH [SRR4018-220Y]	22 uH [SRU1048A-220Y]	22 uH [SRU6011-220Y]	22.1 kOhm [CRT0805-BY-2212ELF]
22 uH [SRR4028-220Y]	22 uH [SRU1063-220Y]	22 uH [SRU6018-220Y]	22.1 Ohm [CAT16-22R1F4LF]
22 uH [SRR5018-220Y]	22 uH [SRU2009-220Y]	22 uH [SRU6025-220Y]	22.1 Ohm [CAT16-22R1F8LF]
22 uH [SRR5028-220Y]	22 uH [SRU2011-220Y]	22 uH [SRU6025A-220Y]	
22 uH [SRR6028-220Y]	22 uH [SRU2013-220Y]	22 uH [SRU8028-220Y]	

Multisim 14.1 Base Edition Components

22.1 Ohm [CAY16-22R1F4LF]	22.6 kOhm [CR1206-FX-2262ELF]	220 kOhm [4116R-1-224]	220 kOhm [4308R-102-224]
22.1 Ohm [CR0402-FX-22R1GLF]	22.6 kOhm [CRT0402-BY-2262GLF]	220 kOhm [4116R-1-224LF]	220 kOhm [4308R-102-224LF]
22.1 Ohm [CR0603-FX-22R1ELF]	22.6 kOhm [CRT0805-BY-2262ELF]	220 kOhm [4116R-2-224]	220 kOhm [4309R-101-224]
22.1 Ohm [CR0603-FX-22R1GLF]	22.6 kOhm [CRT0805-BY-2262ELF]	220 kOhm [4116R-2-224LF]	220 kOhm [4310H-101-224]
22.1 Ohm [CR0805-FX-22R1ELF]	22.6 kOhm [CRT1206-FZ-2262ELF]	220 kOhm [4304M-101-224]	220 kOhm [4310H-101-224LF]
22.1 Ohm [CR1206-FX-22R1ELF]	22.6 Ohm [CR0402-FX-22R6GLF]	220 kOhm [4306R-101-224]	220 kOhm [4310R-101-224]
22.1 Ohm [CR2010-FX-22R1ELF]	22.6 Ohm [CR0603-FX-22R6ELF]	220 kOhm [4306R-101-224LF]	220 kOhm [4310R-101-224LF]
22.1 Ohm [CR2512-FX-22R1ELF]	22.6 Ohm [CR0805-FX-22R6ELF]	220 kOhm [4306R-102-224]	220 kOhm [4310R-102-224]
22.1 Ohm [CRM1206-FX-22R1ELF]	22.6 Ohm [CR1206-FX-22R6ELF]	220 kOhm [4306R-102-224LF]	220 kOhm [4310R-102-224LF]
22.1 Ohm [CRT0805-DW-22R1ELF]	22.6 Ohm [CRT0402-FZ-22R6GLF]	220 kOhm [4308H-101-224LF]	220 kOhm [4416P-1-224]
22.6 kOhm [CR0402-FX-2262GLF]	220 kOhm [4114R-1-224]	220 kOhm [4308M-101-224]	220 kOhm [4604X-101-224LF]
22.6 kOhm [CR0603-FX-2262ELF]	220 kOhm [4114R-1-224LF]	220 kOhm [4308M-102-224]	220 kOhm [4604X-102-224LF]
22.6 kOhm [CR0603-FX-2262ELF]	220 kOhm [4114R-2-224]	220 kOhm [4308M-102-224LF]	220 kOhm [4604X-AP2-224LF]
22.6 kOhm [CR0805-FX-2262ELF]	220 kOhm [4114R-2-224]	220 kOhm [4308R-101-224]	220 kOhm [4605X-101-224LF]
	220 kOhm [4114R-2-224LF]	220 kOhm [4308R-101-224LF]	220 kOhm [4606H-101-224LF]

Multisim 14.1 Base Edition Components

220 kOhm [4606X-101-224LF]	220 kOhm [4814P-1-224LF]	220 kOhm [CAT16-224J8LF]	220 kOhm [CR0603-FX-2203ELF]
220 kOhm [4606X-102-224LF]	220 kOhm [4816P-1-224]	220 kOhm [CAT25-224JALF]	220 kOhm [CR0603-JW-224ELF]
220 kOhm [4606X-AP1-224LF]	220 kOhm [4816P-1-224F]	220 kOhm [CAY10-224J4LF]	220 kOhm [CR0805-FX-2203ELF]
220 kOhm [4608X-101-224LF]	220 kOhm [4816P-1-224LF]	220 kOhm [CAY16-2203F4LF]	220 kOhm [CR0805-JW-224ELF]
220 kOhm [4608X-102-224LF]	220 kOhm [4816P-2-224]	220 kOhm [CAY16-224J4LF]	220 kOhm [CR1206-FX-2203ELF]
220 kOhm [4608X-AP1-224LF]	220 kOhm [4816P-2-224LF]	220 kOhm [CAY16-224J8LF]	220 kOhm [CR1206-JW-224ELF]
220 kOhm [4608X-AP2-224LF]	220 kOhm [4816P-T01-224]	220 kOhm [CHV0603-FX-2203ELF]	220 kOhm [CR1206-JW-224ELF]
220 kOhm [4609X-101-224LF]	220 kOhm [4816P-T01-224LF]	220 kOhm [CHV0805-FX-2203ELF]	220 kOhm [CRM1206-FX-2203ELF]
220 kOhm [4609X-AP1-224LF]	220 kOhm [4816P-T02-224]	220 kOhm [CHV1206-JW-224ELF]	220 kOhm [CRM2512-FX-2203ELF]
220 kOhm [4610X-101-224LF]	220 kOhm [4816P-T02-224LF]	220 kOhm [CHV2010-FX-2203ELF]	220 kOhm [CRM2512-JW-224ELF]
220 kOhm [4610X-102-224LF]	220 kOhm [4820P-1-224]	220 kOhm [CHV2512-FX-2203ELF]	220 kOhm [CRT1206-BX-2203ELF]
220 kOhm [4610X-AP1-224LF]	220 kOhm [4820P-2-224]	220 kOhm [CR0402-FX-2203GLF]	220 kOhm [CRT1206-DX-2203ELF]
220 kOhm [4611X-101-224LF]	220 kOhm [4820P-2-224LF]	220 kOhm [CR0402-JW-224GLF]	
220 kOhm [4612X-102-224LF]	220 kOhm [CAT16-2203F4LF]		
220 kOhm [4814P-1-224]	220 kOhm [CAT16-224J4LF]		

Multisim 14.1 Base Edition Components

220 kOhm [CRT1206-DY- R2203ELF]	220 mOhm [CRM1206-FX- R220ELF]	220 nF [C0603C224K3RACT U]	220 nF [C0805C224K8RACT U]
220 mOhm [CRL0603-FW- R220ELF]	220 mOhm [CRM2010-FX- R220ELF]	220 nF [C0603C224K4RACT U]	220 nF [C0805C224M3VAC TU]
220 mOhm [CRL0603-JW- R220ELF]	220 mOhm [CRM2512-FX- R220ELF]	220 nF [C0603C224K8NAC TU]	220 nF [C0805C224M4VAC TU]
220 mOhm [CRL0805-FW- R220ELF]	220 mOhm [PWR4318WR220JE]	220 nF [C0603C224K8RACT U]	220 nF [C1206C224K1RACT U]
220 mOhm [CRL0805-JW- R220ELF]	220 mOhm [PWR4525NR220F]	220 nF [C0603C224K9RACT U]	220 nF [C1206C224K3RACT U]
220 mOhm [CRL1206-FW- R220ELF]	220 mOhm [PWR4525WR220F E]	220 nF [C0603C224M3VAC TU]	220 nF [C1206C224K4RACT U]
220 mOhm [CRL1206-JW- R220ELF]	220 nF [03066C224KAT2A]	220 nF [C0603C224M4VAC TU]	220 nF [C1206C224K5RACT U]
220 mOhm [CRL2010-FW- R220ELF]	220 nF [0306ZC224KAT2A]	220 nF [C0603C224M8VAC TU]	220 nF [C1206C224M5UAC TU]
220 mOhm [CRL2010-JW- R220ELF]	220 nF [0508YC224KAT2A]	220 nF [C0805C224K3RACT U]	220 nF [C1206F224K3RACT U]
220 mOhm [CRL2512-FW- R220ELF]	220 nF [0508ZC224KAT2S]	220 nF [C0805C224K4RACT U]	220 nF [C1206F224K4RACT U]
220 mOhm [CRL2512-JW- R220ELF]	220 nF [06123C224KAT2W]	220 nF [C0805C224K5RACT U]	220 nF [C1206F224K5RACT U]
	220 nF [0612YC224KAT2V]		
	220 nF [C0402C224K9PACT U]		

Multisim 14.1 Base Edition Components

220 nF [C1210C224K1RACT U]	220 nF [C1812C224K5RACT U]	220 nF [C1825C224M5UAC TU]	220 nF [MDC10224K250A5 2P3TUBE]
220 nF [C1210C224K3GACT U]	220 nF [C1812C224KARACT U]	220 nF [C2220C224K1GACT U]	220 nF [MDC10224K400A5 7P7TUBE]
220 nF [C1210C224K3RACT U]	220 nF [C1812C224M5UAC TU]	220 nF [C2220C224K5GACT U]	220 nF [MDC10224K400A5 7P8TUBE]
220 nF [C1210C224K5RACT U]	220 nF [C1812F224K1RACT U]	220 nF [C2225C224K1RACT U]	220 nF [MDC10224K50A52 P3TUBE]
220 nF [C1210C224M5UAC TU]	220 nF [C1812F224K2RACT U]	220 nF [C2225C224K5RACT U]	220 nF [MDC15224K100B5 3P3TUBE]
220 nF [C1210F224K1RACT U]	220 nF [C1812F224K3RACT U]	220 nF [GMC7.3224K63K33 TR12]	220 nF [MDC15224K250B5 3P3TUBE]
220 nF [C1210F224K3RACT U]	220 nF [C1812F224K5RACT U]	220 nF [LD166C224KAB2A]	220 nF [MDC15224K400B5 3P3TUBE]
220 nF [C1210F224K4RACT U]	220 nF [C1825C224K1RACT U]	220 nF [LD16ZC224KAB2A]	220 nF [MDC15224K50B53 P3TUBE]
220 nF [C1210F224K5RACT U]	220 nF [C1825C224K2RACT U]	220 nF [LG224Z224MAT2S 1]	220 nF [MDK10224K100A5 2P3TUBE]
220 nF [C1812C224K1RACT U]	220 nF [C1825C224K5RACT U]	220 nF [LG226D224MAT2S 1]	220 nF [MDK10224K250A5 2P3TUBE]
220 nF [C1812C224K5HACT U]	220 nF [C1825C224M1UAC TU]	220 nF [MDC10224K100A5 2P3TUBE]	220 nF [MDK10224K50A52 P3TUBE]

Multisim 14.1 Base Edition Components

220 nF [MDS10224K100A5 2P3TUBE]	220 nF [T409A224M035AH 4250]	220 nF [THJA224K035RJN]	220 nH [SRP4020TA-R22Y]
220 nF [MDS10224K250A5 2P3TUBE]	220 nF [T491A224M035AT]	220 nF [TPSA224K035R600 0]	220 nH [SRP5015TA-R22Y]
220 nF [MDS10224K50A52 P3TUBE]	220 nF [T491B224M050AT]	220 nF [TPSA224K050R700 0]	220 nH [SRP7028A- R22Y]
220 nF [MDS15224K100B5 3P3TUBE]	220 nF [T493B224M050AH 6120]	220 nF [W2L1YC224MAT1A]	220 nH [SRP7030- R22FM]
220 nF [MDS15224K250B5 3P3TUBE]	220 nF [T494A224M035AT]	220 nF [W2L1ZC224MAT1S]	220 nH [SRP8040- R22Y]
220 nF [PG224D224MAB2S 1]	220 nF [T494B224M050AT]	220 nF [W3L1YC224MAT1A]	220 Ohm [4114R-1- 221]
220 nF [PG224W224MAB2 S1]	220 nF [T499A224M035AT E18K]	220 nF [W3L1YC224MAT1S]	220 Ohm [4114R-1- 221LF]
220 nF [PG224Z224MAB2S 1]	220 nF [TAJA224K035RNJ]	220 nF [W3L1YC224MAT1S]	220 Ohm [4114R-2- 221]
220 nF [PG226D224MAB2S 1]	220 nF [TAJA224K050RNJ]	220 nH [SRP1038A- R22M]	220 Ohm [4114R-2- 221LF]
220 nF [SPC12.7224K100B 31TR24]	220 nF [TAJB224K050RNJ]	220 nH [SRP1235- R22M]	220 Ohm [4116R-1- 221]
220 nF [SPC16.5224K250C 31TR24]	220 nF [TAJR224K020RNJ]	220 nH [SRP1250- R22M]	220 Ohm [4116R-2- 221]
	220 nF [TAJR224K035RNJ]	220 nH [SRP4012- R22M]	220 Ohm [4116R-2- 221LF]
	220 nF [TAJS224K020RNJ]	220 nH [SRP4012TA-R22M]	220 Ohm [4304M- 101-221]
	220 nF [TAJS224K035RNJ]	220 nH [SRP4020- R22M]	220 Ohm [4304M- 101-221LF]

Multisim 14.1 Base Edition Components

220 Ohm [4304M-102-221]	220 Ohm [4308M-102-221LF]	220 Ohm [4416P-1-221]	220 Ohm [4606X-102-221LF]
220 Ohm [4304M-102-221LF]	220 Ohm [4308R-101-221]	220 Ohm [4416P-1-221LF]	220 Ohm [4606X-AP2-221LF]
220 Ohm [4306H-101-221]	220 Ohm [4308R-101-221LF]	220 Ohm [4416P-2-221]	220 Ohm [4607X-101-221LF]
220 Ohm [4306M-101-221]	220 Ohm [4308R-102-221]	220 Ohm [4416P-T01-221]	220 Ohm [4608H-101-221LF]
220 Ohm [4306M-101-221LF]	220 Ohm [4308R-102-221LF]	220 Ohm [4416P-T02-221]	220 Ohm [4608H-102-221LF]
220 Ohm [4306R-101-221]	220 Ohm [4309R-101-221]	220 Ohm [4420P-1-221]	220 Ohm [4608X-101-221LF]
220 Ohm [4306R-101-221LF]	220 Ohm [4309R-101-221LF]	220 Ohm [4420P-1-221LF]	220 Ohm [4608X-102-221LF]
220 Ohm [4306R-102-221]	220 Ohm [4310H-101-221]	220 Ohm [4420P-2-221]	220 Ohm [4608X-AP2-221LF]
220 Ohm [4306R-102-221LF]	220 Ohm [4310H-101-221LF]	220 Ohm [4420P-T01-221]	220 Ohm [4609H-101-221LF]
220 Ohm [4308H-101-221]	220 Ohm [4310H-102-221]	220 Ohm [4420P-T02-221]	220 Ohm [4609M-101-221LF]
220 Ohm [4308H-101-221LF]	220 Ohm [4310M-101-221]	220 Ohm [4420P-T02-221LF]	220 Ohm [4609X-101-221LF]
220 Ohm [4308H-102-221]	220 Ohm [4310R-101-221]	220 Ohm [4604X-101-221LF]	220 Ohm [4609X-AP1-221LF]
220 Ohm [4308M-101-221]	220 Ohm [4310R-101-221LF]	220 Ohm [4604X-102-221LF]	220 Ohm [4610H-101-221LF]
220 Ohm [4308M-101-221LF]	220 Ohm [4310R-102-221]	220 Ohm [4605X-101-221LF]	220 Ohm [4610X-101-221LF]
220 Ohm [4308M-102-221]	220 Ohm [4310R-102-221LF]	220 Ohm [4606X-101-221LF]	220 Ohm [4610X-102-221LF]

Multisim 14.1 Base Edition Components

220 Ohm [4611X-101-221LF]	220 Ohm [4816P-2-221]	220 Ohm [CAT16-221J4LF]	220 Ohm [CR0805-FX-2200ELF]
220 Ohm [4612X-102-221LF]	220 Ohm [4816P-2-221F]	220 Ohm [CAT16-221J8LF]	220 Ohm [CR0805-FX-2200GLF]
220 Ohm [4613X-101-221LF]	220 Ohm [4816P-2-221LF]	220 Ohm [CAT25-221JALF]	220 Ohm [CR0805-JW-221ELF]
220 Ohm [4614X-101-221LF]	220 Ohm [4816P-T01-221]	220 Ohm [CAY10-221J4LF]	220 Ohm [CR0805-JW-221GLF]
220 Ohm [4614X-102-221LF]	220 Ohm [4816P-T01-221LF]	220 Ohm [CAY16-2200F4LF]	220 Ohm [CR1206-FX-2200ELF]
220 Ohm [4814P-1-221]	220 Ohm [4816P-T02-221]	220 Ohm [CAY16-221J4GLF]	220 Ohm [CR1206-JW-221ELF]
220 Ohm [4814P-1-221LF]	220 Ohm [4816P-T02-221LF]	220 Ohm [CAY16-221J4LF]	220 Ohm [CR2010-JW-221ELF]
220 Ohm [4814P-2-221]	220 Ohm [4820P-1-221]	220 Ohm [CAY16-221J8LF]	220 Ohm [CR2512-JW-221ELF]
220 Ohm [4814P-2-221LF]	220 Ohm [4820P-1-221LF]	220 Ohm [CAY17-221JALF]	220 Ohm [CRM1206-FX-2200ELF]
220 Ohm [4814P-T01-221]	220 Ohm [4820P-2-221]	220 Ohm [CR0201-FW-2200GLF]	220 Ohm [CRM2512-FX-2200ELF]
220 Ohm [4814P-T01-221LF]	220 Ohm [4820P-T01-221]	220 Ohm [CR0402-FX-2200GLF]	220 Ohm [CRM2512-JW-221ELF]
220 Ohm [4814P-T02-221]	220 Ohm [4820P-T02-221]	220 Ohm [CR0402-JW-221GLF]	220 Ohm [PWR2615W2200J]
220 Ohm [4814P-T02-221LF]	220 Ohm [CAT10-221J4LF]	220 Ohm [CR0603-FX-2200ELF]	220 Ohm [PWR2615W2200JE]
220 Ohm [4816P-1-221]	220 Ohm [CAT16-2200F4LF]	220 Ohm [CR0603-JW-221ELF]	
220 Ohm [4816P-1-221LF]	220 Ohm [CAT16-221J2LF]	220 Ohm [CR0603-JW-221GLF]	

Multisim 14.1 Base Edition Components

220 Ohm [PWR263S-35- 2200FE]	220 pF [C0402C221K5RACT U]	220 pF [C0805C221K1GACT U]	220 pF [C1206C221K1GACT U]
220 Ohm [PWR263S-35- 2200J]	220 pF [C0402C221K8RACT U]	220 pF [C0805C221K1RACT U]	220 pF [C1206C221K2GACT U]
220 Ohm [PWR4525W2200J]	220 pF [C0603C221K1RACT U]	220 pF [C0805C221K2GACT U]	220 pF [C1206C221K5GACT U]
220 Ohm [PWR4525W2200JE]	220 pF [C0603C221K2RACT U]	220 pF [C0805C221K2RACT U]	220 pF [C1206C221KBGAC TU]
220 Ohm [PWR6327W2200J]	220 pF [C0603C221K3GACT U]	220 pF [C0805C221K3GACT U]	220 pF [C1206C221KCGAC TU]
220 Ohm [PWR6327W2200JE]	220 pF [C0603C221K3RACT U]	220 pF [C0805C221K3RACT U]	220 pF [C1206C221KDGAC TU]
220 pF [C0402C221K1HACT U]	220 pF [C0603C221K4GACT U]	220 pF [C0805C221K4RACT U]	220 pF [C1210C221K1GACT U]
220 pF [C0402C221K3HACT U]	220 pF [C0603C221K4RACT U]	220 pF [C0805C221K5GACT U]	220 pF [C1210C221KBGAC TU]
220 pF [C0402C221K3RACT U]	220 pF [C0603C221K5GACT U]	220 pF [C0805C221K5RACT U]	220 pF [C1812C221KBGAC TU]
220 pF [C0402C221K4RACT U]	220 pF [C0603C221K5RACT U]	220 pF [C0805C221K8RACT U]	220 pF [C1825C221KBGAC TU]
220 pF [C0402C221K5GACT U]	220 pF [C0603C221K8RACT U]	220 pF [C0805C221KARACT U]	220 pF [C2220C221KBGAC TU]
220 pF [C0402C221K5HACT U]			

Multisim 14.1 Base Edition Components

220 pF [C2225C221KBGAC TU]	220 uF [2R5TPE220MAPB]	220 uF [6SVPC220MV]	220 uF [A700V227M002AT E009]
220 pF [CA064C221K5GAC TU]	220 uF [2R5TPE220MAZB]	220 uF [6SVPE220M]	220 uF [A700X227M004AT E010]
220 pF [CDR02BP221BKSM]	220 uF [2R5TPE220MF]	220 uF [6SVPE220MW]	220 uF [A700X227M004AT E015]
220 pF [W2F11A2218AT1A]	220 uF [2R5TPE220MI]	220 uF [6TPE220M]	220 uF [A700X227M2R5AT E010]
220 pF [W3F11A2218AT1A]	220 uF [2R5TPE220MLB]	220 uF [6TPE220MAP]	220 uF [A700X227M2R5AT E015]
220 uF [10TPB220M]	220 uF [2R5TPG220M]	220 uF [6TPE220MI]	220 uF [EEFCX0D221R]
220 uF [10TPB220ML]	220 uF [2R5TPG220MUG]	220 uF [6TPF220M5L]	220 uF [EEFCX0E221R]
220 uF [10TPE220MIL]	220 uF [2TPF220M6]	220 uF [6TPF220M9L]	220 uF [EEFCX0G221R]
220 uF [10TPE220ML]	220 uF [4TPE220M]	220 uF [6TPF220ML]	220 uF [EEFCX0G221XR]
220 uF [16SEPC220MD]	220 uF [4TPE220MAZB]	220 uF [A700D227M002AT E015]	220 uF [EEFCX0J221R]
220 uF [2R5TPE220M]	220 uF [4TPE220MF]	220 uF [A700D227M002AT E018]	220 uF [EEFLR0D221R]
220 uF [2R5TPE220M9]	220 uF [4TPE220MI]	220 uF [A700D227M004AT E009]	220 uF [EEFLR0D221R4]
220 uF [2R5TPE220MAFB]	220 uF [4TPG220M]		220 uF [EEFLS0D221R]
	220 uF [6SVPC220M]		

Multisim 14.1 Base Edition Components

220 uF [EEFSR0D221R]	220 uF [T491D227M010AT]	220 uF [T494E227M016AT]	220 uF [T495D227M010AT E075]
220 uF [EEFSR0D221R4]	220 uF [T491D227M2R5AT]	220 uF [T494V227M004AT]	220 uF [T495D227M010AT E100]
220 uF [EEFS0D221R]	220 uF [T491E227M016AT]	220 uF [T494V227M006AT]	220 uF [T495D227M010AT E125]
220 uF [EEFSX0D221ER]	220 uF [T491V227M004AT]	220 uF [T494X227M006AT]	220 uF [T495D227M010AT E045]
220 uF [EEFSX0E221E7]	220 uF [T491V227M006AT]	220 uF [T494X227M010AT]	220 uF [T495D227M2R5AT E045]
220 uF [EEFSX0E221ER]	220 uF [T491X227M006AT]	220 uF [T494X227M016AT]	220 uF [T495E227M016AT E050]
220 uF [EEFSX0G221ER]	220 uF [T491X227M010AT]	220 uF [T495C227M006AT E225]	220 uF [T495E227M016AT E075]
220 uF [EEHZA1E221P]	220 uF [T491X227M016AT]	220 uF [T495D227M004AT E040]	220 uF [T495E227M016AT E150]
220 uF [EEHZC1E221P]	220 uF [T494B227M004AT]	220 uF [T495D227M004AT E050]	220 uF [T495X227M006AT E100]
220 uF [ETPH220MABC]	220 uF [T494C227M006AT]	220 uF [T495D227M004AT E100]	220 uF [T495X227M010AT E045]
220 uF [T419H227M004AH 4250]	220 uF [T494D227M006AT]	220 uF [T495D227M006AT E045]	220 uF [T495X227M010AT E050]
220 uF [T491B227M004AT]	220 uF [T494D227M010AT]	220 uF [T495D227M006AT E100]	220 uF [T495X227M010AT E060]
220 uF [T491C227M006AT]	220 uF [T494D227M2R5AT]	220 uF [T495D227M010AT E045]	

Multisim 14.1 Base Edition Components

220 uF [T495X227M010AT E070]	220 uF [T520B227M004AT E070]	220 uF [T520C227M004AT E055]	220 uF [T520D227M006AT E050]
220 uF [T495X227M010AT E100]	220 uF [T520B227M006AT E035]	220 uF [T520C227M006AT E025]	220 uF [T520D227M010AT E018]
220 uF [T495X227M016AT E100]	220 uF [T520B227M2R5AT E015]	220 uF [T520C227M006AT E045]	220 uF [T520D227M010AT E025]
220 uF [T496X227M010AT 6110]	220 uF [T520B227M2R5AT E018]	220 uF [T520C227M2R5AT E025]	220 uF [T520D227M010AT E040]
220 uF [T498X227M010AT E500]	220 uF [T520B227M2R5AT E025]	220 uF [T520D227M004AT E012]	220 uF [T520D227M2R5AT E007]
220 uF [T510X227M016AT E025]	220 uF [T520B227M2R5AT E030]	220 uF [T520D227M004AT E065]	220 uF [T520D227M2R5AT E040]
220 uF [T510X227M016AT E040]	220 uF [T520B227M2R5AT E035]	220 uF [T520D227M006AT E006]	220 uF [T520U227M2R5AT E055]
220 uF [T513X227M016AH 6110]	220 uF [T520B227M2R5AT E070]	220 uF [T520D227M006AT E007]	220 uF [T520V227M004AT E006]
220 uF [T513X227M016AH 6120]	220 uF [T520C227M004AT E018]	220 uF [T520D227M006AT E009]	220 uF [T520V227M004AT E007]
220 uF [T520B227M004AT E035]	220 uF [T520C227M004AT E025]	220 uF [T520D227M006AT E015]	220 uF [T520V227M004AT E009]
220 uF [T520B227M004AT E045]	220 uF [T520C227M004AT E045]	220 uF [T520D227M006AT E040]	220 uF [T520V227M004AT E012]

Multisim 14.1 Base Edition Components

220 uF [T520V227M004AT E015]	220 uF [T520V227M006AT E040]	220 uF [T522V227M006AT E025]	220 uF [T530D227M006AT E006]
220 uF [T520V227M004AT E018]	220 uF [T520V227M010AT E045]	220 uF [T522V227M006AT E040]	220 uF [T530D227M010AT E006]
220 uF [T520V227M004AT E025]	220 uF [T520V227M2R5AT E007]	220 uF [T525D227M004AT E025]	220 uF [T530D227M010AT E010]
220 uF [T520V227M004AT E040]	220 uF [T520V227M2R5AT E009]	220 uF [T525D227M006AT E025]	220 uF [T530Y227M010AT E006]
220 uF [T520V227M004AT E045]	220 uF [T520V227M2R5AT E012]	220 uF [T525D227M010AT E025]	220 uF [T541D227M010AH 6510]
220 uF [T520V227M006AT E007]	220 uF [T520V227M2R5AT E015]	220 uF [T528Z227M004AT E007]	220 uF [T543V227M004AT E015]
220 uF [T520V227M006AT E009]	220 uF [T520V227M2R5AT E025]	220 uF [T528Z227M004AT E009]	220 uF [TAJB227K002RNJ]
220 uF [T520V227M006AT E012]	220 uF [T520V227M2R5AT E045]	220 uF [T528Z227M004AT E012]	220 uF [TAJC227K004RNJ]
220 uF [T520V227M006AT E015]	220 uF [T520W227M004AT E025]	220 uF [T528Z227M006AT E009]	220 uF [TAJC227K006RNJ]
220 uF [T520V227M006AT E018]	220 uF [T520W227M004AT E040]	220 uF [T528Z227M006AT E012]	220 uF [TAJD227K004RNJ]
220 uF [T520V227M006AT E025]	220 uF [T520Y227M010AT E040]	220 uF [T530D227M006AT E005]	220 uF [TAJD227K006RNJ]
			220 uF [TAJD227K010RNJ]

Multisim 14.1 Base Edition Components

220 uF [TAJE227K006RNJ]	220 uF [TPSC227K006R010 0]	220 uF [TPSD227K010R015 0]	220 uF [TPSV227K016R007 5]
220 uF [TAJE227K010RNJ]	220 uF [TPSC227K006R012 5]	220 uF [TPSE227K006R010 0]	220 uF [TPSV227K016R010 0]
220 uF [TAJE227K016RNJ]	220 uF [TPSC227K006R025 0]	220 uF [TPSE227K010R005 0]	220 uF [TPSV227K016R015 0]
220 uF [TAJV227K016RNJ]	220 uF [TPSD227K004R004 0]	220 uF [TPSE227K010R006 0]	220 uF [TPSY227K004R004 0]
220 uF [TAJW227K004RNJ]	220 uF [TPSD227K004R005 0]	220 uF [TPSE227K010R007 0]	220 uF [TPSY227K006R010 0]
220 uF [TAJY227K006RNJ]	220 uF [TPSD227K004R010 0]	220 uF [TPSE227K010R010 0]	220 uF [TPSY227K006R015 0]
220 uF [THJE227K010RJN]	220 uF [TPSD227K006R005 0]	220 uF [TPSE227K010R012 5]	220 uF [TPSY227K010R010 0]
220 uF [TPME227K016R00 25]	220 uF [TPSD227K006R010 0]	220 uF [TPSE227K010R015 0]	220 uF [TPSY227K010R015 0]
220 uF [TPME227K016R00 40]	220 uF [TPSD227K006R012 5]	220 uF [TPSE227K016R010 0]	220 uF [TPSY227K010R020 0]
220 uF [TPSB227K002R060 0]	220 uF [TPSD227K010R005 0]	220 uF [TPSE227K016R015 0]	220 uF [TRJD227K010RRJ]
220 uF [TPSC227K006R007 0]	220 uF [TPSD227K010R010 0]	220 uF [TPSV227K016R005 0]	220 uF [TRJE227K010RRJ]
			220 uH [SDE0805A- 221K]

Multisim 14.1 Base Edition Components

220 uH [SDE1006A-221K]	220 uH [SDR1307A-221K]	220 uH [SRR0905-221K]	220 uH [SRR4028-221Y]
220 uH [SDR0302-221KL]	220 uH [SDR1806-221KL]	220 uH [SRR0906-221YL]	220 uH [SRR5018-221Y]
220 uH [SDR0403-221KL]	220 uH [SDR6603-221M]	220 uH [SRR0908-221YL]	220 uH [SRR5028-221Y]
220 uH [SDR0503-221KL]	220 uH [SDR7030-221K]	220 uH [SRR1003-221M]	220 uH [SRR6028-221Y]
220 uH [SDR0603-221KL]	220 uH [SDR7045-221K]	220 uH [SRR1005-221K]	220 uH [SRR6603-221ML]
220 uH [SDR0604-221KL]	220 uH [SRN1060-221M]	220 uH [SRR1205-221KL]	220 uH [SRR7032-221M]
220 uH [SDR0703-221KL]	220 uH [SRN4018-221M]	220 uH [SRR1206-221KL]	220 uH [SRR7045-221M]
220 uH [SDR0805-221KL]	220 uH [SRN4026-221M]	220 uH [SRR1208-221KL]	220 uH [SRU1038-221Y]
220 uH [SDR0906-221KL]	220 uH [SRN6045-221M]	220 uH [SRR1210-221M]	220 uH [SRU1038A-221Y]
220 uH [SDR1005-221KL]	220 uH [SRR0603-221KL]	220 uH [SRR1210A-221M]	220 uH [SRU1048-221Y]
220 uH [SDR1006-221KL]	220 uH [SRR0604-221KL]	220 uH [SRR1240-221K]	220 uH [SRU1048A-221Y]
220 uH [SDR1030-221K]	220 uH [SRR0735A-221M]	220 uH [SRR1260-221K]	220 uH [SRU6025-221Y]
220 uH [SDR1045-221K]	220 uH [SRR0745A-221M]	220 uH [SRR1260A-221K]	220 uH [SRU6025A-221Y]
220 uH [SDR1305-221K]	220 uH [SRR0804-221K]	220 uH [SRR1280-221K]	221 kOhm [CR0402-FX-2213GLF]
220 uH [SDR1307-221KL]	220 uH [SRR0805-221K]	220 uH [SRR1806-221M]	221 kOhm [CR0603-FX-2213ELF]

Multisim 14.1 Base Edition Components

221 kOhm [CR0805-FX- 2213ELF]	226 kOhm [CR0402-FX- 2263GLF]	23.2 kOhm [CR0603-FX- 2322ELF]	23.7 kOhm [CRM2010-FX- 2372ELF]
221 kOhm [CR1206-FX- 2213ELF]	226 kOhm [CR0603-FX- 2263ELF]	23.2 kOhm [CR0805-FX- 2322ELF]	23.7 kOhm [CRM2512-FT- 2372ELF]
221 kOhm [CRT0603-AZ- 2213ELF]	226 kOhm [CR0805-FX- 2263ELF]	23.2 kOhm [CR1206-FX- 2322ELF]	23.7 kOhm [CRT0603-BX- 2372ELF]
221 Ohm [CAT16- 2210F4LF]	226 kOhm [CR1206-FX- 2263ELF]	23.2 kOhm [CRT0402-BY- 2322GLF]	23.7 kOhm [CRT0603-BX- 2372LF]
221 Ohm [CAY16- 2210F4LF]	226 Ohm [CAY16- 2260F4LF]	23.2 kOhm [CRT0805-BY- 2322ELF]	23.7 kOhm [CRT0805-BZ- 2372ELF]
221 Ohm [CR0402- FX-2210GLF]	226 Ohm [CR0402- FX-2260GLF]	23.2 kOhm [CRT0805-CX- 2322ELF]	23.7 kOhm [CRT0805-FV- 2372ELF]
221 Ohm [CR0603- FX-2210ELF]	226 Ohm [CR0603- FX-2260ELF]	23.2 Ohm [CR0603- FX-23R2ELF]	23.7 Ohm [CR0402- FX-23R7GLF]
221 Ohm [CR0603- FX-2210HLF]	226 Ohm [CR0805- FX-2260ELF]	23.2 Ohm [CR1206- FX-23R2ELF]	23.7 Ohm [CR0603- FX-23R7ELF]
221 Ohm [CR0805- FX-2210ELF]	226 Ohm [CR1206- FX-2260ELF]	23.7 kOhm [CR0402-FX- 2372GLF]	23.7 Ohm [CR0805- FX-23R7ELF]
221 Ohm [CR0805- FX-2210GLF]	226 Ohm [CR2010- FX-2260ELF]	23.7 kOhm [CR0603-FX- 2372ELF]	23.7 Ohm [CR1206- FX-23R7ELF]
221 Ohm [CR1206- FX-2210ELF]	226 Ohm [CRT1206-FZ- 2260ELF]	23.7 kOhm [CR0805-FX- 2372ELF]	232 kOhm [CR0402-FX- 2323GLF]
221 Ohm [CR2512- FX-2210ELF]	23 kOhm [4608X- 101-233LF]	23.7 kOhm [CR1206-FX- 2372ELF]	232 kOhm [CR0603-FX- 2323ELF]
221 Ohm [CRM1206-FX- 2210ELF]	23.2 kOhm [CR0402-FX- 2322GLF]		

Multisim 14.1 Base Edition Components

232 kOhm [CR0805-FX- 2323ELF]	237 Ohm [CR1206- FX-2370ELF]	24 kOhm [CR0402- FX-2402GLF]	24 mOhm [PWR4525WR024J]
232 kOhm [CR1206-FX- 2323ELF]	237 Ohm [CRT0402-FZ- 2370GLF]	24 kOhm [CR0603- FX-2402ELF]	24 mOhm [PWR4525WR024JE]
232 Ohm [CR0603- FX-2320ELF]	24 kOhm [4114R-1- 243]	24 kOhm [CR0603- FX-2402GLF]	24 mOhm [PWR6327WR024J]
232 Ohm [CR0805- FX-2320ELF]	24 kOhm [4114R-1- 243LF]	24 kOhm [CR0603- JW-243ELF]	24 mOhm [PWR6327WR024JE]
232 Ohm [CR1206- FX-2320ELF]	24 kOhm [4116R-1- 243]	24 kOhm [CR0805- FX-2402ELF]	24 Ohm [4114R-1- 240]
237 kOhm [CR0402-FX- 2373GLF]	24 kOhm [4116R-1- 243LF]	24 kOhm [CR0805- JW-243ELF]	24 Ohm [4114R-1- 240LF]
237 kOhm [CR0603-FX- 2373ELF]	24 kOhm [4308H- 101-243]	24 kOhm [CR1206- FX-2402ELF]	24 Ohm [4116R-1- 240LF]
237 kOhm [CR0603-FX- 2373ELF]	24 kOhm [4308M- 102-243]	24 kOhm [CR1206- JW-243ELF]	24 Ohm [CAT10- 240J4LF]
237 kOhm [CR0805-FX- 2373ELF]	24 kOhm [4308M- 102-243LF]	24 kOhm [CRM2010-FT- 2402ELF]	24 Ohm [CAT16- 240J4GLF]
237 kOhm [CR1206-FX- 2373ELF]	24 kOhm [4608X- 101-243LF]	24 kOhm [CRS2010-FX- 2402ELF]	24 Ohm [CAT16- 240J4LF]
237 kOhm [CRT0805-BY- 2373ELF]	24 kOhm [CAT16- 2402F4LF]	24 mOhm [PWR1913WR024J]	24 Ohm [CAT25- 240JALF]
237 Ohm [CR0402- FX-2370GLF]	24 kOhm [CAY10- 243J4LF]	24 mOhm [PWR1913WR024JE]	24 Ohm [CAY10- 240J2LF]
237 Ohm [CR0603- FX-2370ELF]	24 kOhm [CAY16- 243J8LF]	24 mOhm [PWR2615WR024J]	24 Ohm [CAY10- 240J4LF]
237 Ohm [CR0805- FX-2370ELF]	24 kOhm [CR0201- FW-2402GLF]	24 mOhm [PWR2615WR024JE]	24 Ohm [CAY16- 240J4LF]

Multisim 14.1 Base Edition Components

24 Ohm [CAY16-24R0F4LF]	24 Ohm [PWR2010W24R0JE]	24 pF [C1812C240KBGAC TU]	24.3 Ohm [CR1206-FX-24R3ELF]
24 Ohm [CAY17-240JALF]	24 Ohm [PWR3014W24R0JE]	24 pF [C1825C240KBGAC TU]	24.3 Ohm [CRM1206-FX-24R3ELF]
24 Ohm [CR0402-FX-24R0GLF]	24 Ohm [PWR4318W24R0JE]	24 pF [C1825C240KCGAC TU]	24.9 kOhm [CAT16-2492F4LF]
24 Ohm [CR0402-JW-240GLF]	24 Ohm [PWR5322W24R0JE]	24 pF [C2220C240KBGAC TU]	24.9 kOhm [CAY16-2492F4LF]
24 Ohm [CR0603-FX-24R0ELF]	24 pF [C0402C240K4GACT U]	24 pF [C2225C240KBGAC TU]	24.9 kOhm [CR0402-FX-2492GLF]
24 Ohm [CR0603-JW-240ELF]	24 pF [C0402C240K5GACT U]	24.3 kOhm [CR0402-FX-2432GLF]	24.9 kOhm [CR0603-FX-2492ELF]
24 Ohm [CR0805-FX-24R0ELF]	24 pF [C0603C240K2GACT U]	24.3 kOhm [CR0603-FX-2432ELF]	24.9 kOhm [CR0805-FX-2492ELF]
24 Ohm [CR0805-JW-240ELF]	24 pF [C0805C240K5GACT U]	24.3 kOhm [CR0805-FX-2432ELF]	24.9 kOhm [CR1206-FX-2492ELF]
24 Ohm [CR1206-FX-24R0ELF]	24 pF [C0805C240KBGAC TU]	24.3 kOhm [CR1206-FX-2432ELF]	24.9 kOhm [CR2512-FX-2492ELF]
24 Ohm [CR1206-JW-240ELF]	24 pF [C1206C240KBGAC TU]	24.3 Ohm [CR0402-FX-24R3GLF]	24.9 kOhm [CRM2512-FX-2492ELF]
24 Ohm [CRM2512-FX-24R0ELF]	24 pF [C1210C240KBGAC TU]	24.3 Ohm [CR0603-FX-24R3ELF]	24.9 kOhm [CRT0402-BY-2492GLF]
24 Ohm [CRM2512-JW-240ELF]		24.3 Ohm [CR0805-FX-24R3ELF]	24.9 kOhm [CRT0402-FZ-2492GLF]

Multisim 14.1 Base Edition Components

24.9 kOhm [CRT0603-BY- 2492ELF]	24.9 Ohm [CRT0402-BY- 24R9GLF]	240 kOhm [CR1206-FX- 2403ELF]	240 mOhm [CRL2512-FW- R240ELF]
24.9 kOhm [CRT0603-PW- 2492ELF]	24.9 Ohm [CRT0603-BY- 24R9ELF]	240 kOhm [CR1206-JW- 244ELF]	240 mOhm [CRL2512-JW- R240ELF]
24.9 kOhm [CRT0805-DY- 2492ELF]	24.9 Ohm [CRT1206-BY- 24R9ELF]	240 kOhm [CRT1206-BY- 2403ELF]	240 mOhm [CRM2010-FX- R240ELF]
24.9 kOhm [CRT1206-BY- 2492ELF]	24.9 Ohm [CRT1206-DY- 24R9ELF]	240 mOhm [CRL0603-FW- R240ELF]	240 mOhm [CRM2512-FX- R240ELF]
24.9 Ohm [CAT16- 24R9F4LF]	240 kOhm [CAY16- 244J4LF]	240 mOhm [CRL0603-JW- R240ELF]	240 nH [SRN2010- R24M]
24.9 Ohm [CAY16- 24R9F4LF]	240 kOhm [CHV1206-FX- 2403ELF]	240 mOhm [CRL0805-FW- R240ELF]	240 nH [SRN2012- R24M]
24.9 Ohm [CR0201- FW-24R9GLF]	240 kOhm [CR0402-FX- 2403GLF]	240 mOhm [CRL0805-JW- R240ELF]	240 nH [SRN2510- R24M]
24.9 Ohm [CR0402- FX-24R9GLF]	240 kOhm [CR0603-FX- 2403ELF]	240 mOhm [CRL1206-FW- R240ELF]	240 nH [SRN2512- R24M]
24.9 Ohm [CR0603- FX-24R9ELF]	240 kOhm [CR0603-JW- 244ELF]	240 mOhm [CRL1206-JW- R240ELF]	240 Ohm [4114R-1- 241]
24.9 Ohm [CR0603- FX-24R9GLF]	240 kOhm [CR0805-FX- 2403ELF]	240 mOhm [CRL2010-FW- R240ELF]	240 Ohm [4114R-2- 241]
24.9 Ohm [CR0805- FX-24R9ELF]	240 kOhm [CR0805-JW- 244ELF]	240 mOhm [CRL2010-JW- R240ELF]	240 Ohm [4116R-1- 241LF]
24.9 Ohm [CR1206- FX-24R9ELF]	240 kOhm [CR0805-FX- 2403ELF]	240 mOhm [CRL2010-JW- R240ELF]	240 Ohm [4116R-2- 241]
24.9 Ohm [CRM2512-FX- 24R9ELF]	240 kOhm [CR0805-JW- 244ELF]	240 mOhm [CRL2010-JW- R240ELF]	240 Ohm [4308R- 101-241]

Multisim 14.1 Base Edition Components

240 Ohm [4308R-102-241]	240 Ohm [CR0402-JW-241GLF]	240 pF [C0402C241K1HACT U]	243 kOhm [CR0402-FX-2433GLF]
240 Ohm [4308R-102-241LF]	240 Ohm [CR0603-FX-2400ELF]	240 pF [C0402C241K3HACT U]	243 kOhm [CR0603-FX-2433ELF]
240 Ohm [4310R-101-241]	240 Ohm [CR0603-JW-241ELF]	240 pF [C0402C241K5HACT U]	243 kOhm [CR0805-FX-2433ELF]
240 Ohm [4606X-101-241LF]	240 Ohm [CR0603-JW-241GLF]	240 pF [C0603C241K5GACT U]	243 kOhm [CR1206-FX-2433ELF]
240 Ohm [4608X-102-241LF]	240 Ohm [CR0805-FX-2400ELF]	240 pF [C0805C241K5GACT U]	243 Ohm [CAY16-2430F4LF]
240 Ohm [4609X-AP1-241LF]	240 Ohm [CR0805-JW-241ELF]	240 pF [C1206C241KBGAC TU]	243 Ohm [CR0402-FX-2430GLF]
240 Ohm [4816P-2-241]	240 Ohm [CR1206-FX-2400ELF]	240 pF [C1210C241KBGAC TU]	243 Ohm [CR0603-FX-2430ELF]
240 Ohm [4816P-2-241LF]	240 Ohm [CR1206-JW-241ELF]	240 pF [C1812C241KBGAC TU]	243 Ohm [CR0805-FX-2430ELF]
240 Ohm [CAT10-241J4LF]	240 Ohm [CR2010-JW-241ELF]	240 pF [C1825C241KBGAC TU]	243 Ohm [CR1206-FX-2430ELF]
240 Ohm [CAT16-2400F4LF]	240 Ohm [CRM1206-FX-2400ELF]	240 pF [C2220C241KBGAC TU]	2462
240 Ohm [CAT16-241J4LF]	240 Ohm [CRT0402-DZ-2400GLF]	240 pF [C2225C241KBGAC TU]	2466
240 Ohm [CAT25-241JALF]	240 Ohm [PWR220T-20-2400F]		2468
240 Ohm [CAY10-241J4LF]	240 Ohm [PWR263S-35-2400J]		2477
240 Ohm [CAY16-241J4LF]			2481
240 Ohm [CR0402-FX-2400GLF]			

Multisim 14.1 Base Edition Components

249 kOhm [CR0201-FW- 2493GLF]	249 mOhm [PWR4525WR249JE]	25 kOhm [4116R-1- 253]	25 mOhm [PWR221T-30- R025J]
249 kOhm [CR0402-FX- 2493GLF]	249 mOhm [PWR6327WR249J]	25 kOhm [4116R-2- 253]	25 mOhm [PWR4412- 2SBR0250F]
249 kOhm [CR0603-FX- 2493ELF]	249 mOhm [PWR6327WR249JE]	25 kOhm [CRT1206-PV- 2502ELF]	25 mOhm [PWR4412- 2SCR0250F]
249 kOhm [CR0805-FX- 2493ELF]	249 Ohm [CR0402- FX-2490GLF]	25 kOhm [PWR163S-25- 2502F]	25 mOhm [PWR4412- 2SCR0250J]
249 kOhm [CR1206-FX- 2493ELF]	249 Ohm [CR0603- FX-2490ELF]	25 kOhm [PWR163S-25- 2502J]	25 mOhm [PWR4412- 2SDR0250F]
249 kOhm [CRT0603-BY- 2493ELF]	249 Ohm [CR0805- FX-2490ELF]	25 kOhm [PWR6327W2502JE]	25 Ohm [4116R-1- 250]
249 kOhm [CRT0805-BY- 2493ELF]	249 Ohm [CR1206- FX-2490ELF]	25 mOhm [CRA2512-FZ- R025ELF]	25 Ohm [4116R-1- 250LF]
249 mOhm [PWR1913WR249J]	249 Ohm [CRM0805-FX- 2490ELF]	25 mOhm [CRA2512-JZ- R025ELF]	25 Ohm [4310M- 102-250]
249 mOhm [PWR1913WR249JE]	249 Ohm [CRM2512-FX- 2490ELF]	25 mOhm [CRF2512-FZ- R025ELF]	25 Ohm [4310M- 102-250LF]
249 mOhm [PWR2615WR249J]	249 Ohm [CRT0603-BY- 2490ELF]	25 mOhm [PWR163S-25- R025J]	25 Ohm [4420P- T01-250]
249 mOhm [PWR2615WR249JE]	249 Ohm [CRT1206-BY- 2490ELF]	25 mOhm [PWR163S-25- R025JE]	25 Ohm [4816P-1- 250]
249 mOhm [PWR4525WR249J]	249 Ohm [CRT1206-PV- 2490ELF]	25 mOhm [PWR220T-35- R025J]	25 Ohm [PWR163S-25- 25R0FE]

Multisim 14.1 Base Edition Components

25 Ohm [PWR220T-20-25R0J]	25.5 kOhm [CRT0805-BW-2552ELF]	250 mOhm [PWR163S-25-R250J]	250 Ohm [PWR163S-25-2500FE]
25 Ohm [PWR220T-35-25R0J]	25.5 kOhm [CRT0805-BY-2552ELF]	250 mOhm [PWR2010WR250JE]	250 Ohm [PWR220T-35-2500J]
25 Ohm [PWR221T-30-25R0F]	25.5 kOhm [CRT1206-BW-2552ELF]	250 mOhm [PWR221T-30-R250F]	250 Ohm [PWR263S-35-2500F]
25 Ohm [PWR221T-30-25R0J]	25.5 Ohm [CAT16-25R5F4LF]	250 mOhm [PWR263S-35-R250F]	250 Ohm [PWR263S-35-2500FE]
25 Ohm [PWR263S-20-25R0J]	25.5 Ohm [CR0402-FX-25R5GLF]	250 mOhm [PWR4318WR250JE]	250 Ohm [PWR263S-35-2500JE]
25.5 kOhm [CR0402-FX-2552GLF]	25.5 Ohm [CR0603-FX-25R5ELF]	250 mOhm [PWR5322WR250JE]	250 Ohm [PWR4318W2500JE]
25.5 kOhm [CR0603-FX-2552ELF]	25.5 Ohm [CR1206-FX-25R5ELF]	250 Ohm [4116R-1-251]	2-534206-0
25.5 kOhm [CR0805-FX-2552ELF]	25.5 Ohm [PWR4525W25R5F]	250 Ohm [4310R-101-251]	255 kOhm [CR0402-FX-2553GLF]
25.5 kOhm [CR1206-FX-2552ELF]	25 AMP	250 Ohm [4310R-101-251LF]	255 kOhm [CR0603-FX-2553ELF]
25.5 kOhm [CRM2512-FX-2552ELF]	250 mOhm [CRM2512-FX-R250ELF]	250 Ohm [4420P-1-251]	255 kOhm [CR0805-FX-2553ELF]
25.5 kOhm [CRM2512-FX-2552ELF]	250 mOhm [PWR163S-25-R250F]	250 Ohm [4609X-101-251LF]	255 kOhm [CR1206-FX-2553ELF]
25.5 kOhm [CRT0402-BY-2552GLF]	250 mOhm [PWR163S-25-R250FE]	250 Ohm [CAT16-251J4LF]	255 kOhm [CRT0805-BY-2553ELF]
		250 Ohm [CRT1206-PW-2500ELF]	

Multisim 14.1 Base Edition Components

255 Ohm [CR0603-FX-2550ELF]	26.1 Ohm [CR0805-FX-26R1ELF]	26.7 kOhm [CRT1206-BY-2672ELF]	261 Ohm [CR0603-FX-2610ELF]
255 Ohm [CR0805-FX-2550ELF]	26.1 Ohm [CR1206-FX-26R1ELF]	26.7 Ohm [CAY16-26R7F4LF]	261 Ohm [CR0805-FX-2610ELF]
255 Ohm [CR1206-FX-2550ELF]	26.1 Ohm [CRM1206-FX-26R1ELF]	26.7 Ohm [CR0402-FX-26R7GLF]	261 Ohm [CR1206-FX-2610ELF]
255 Ohm [CR2010-FX-2550ELF]	26.1 Ohm [CRM2512-FX-26R1ELF]	26.7 Ohm [CR0603-FX-26R7ELF]	261 Ohm [CRM1206-FX-2610ELF]
255 Ohm [CRT1206-BY-2550ELF]	26.1 Ohm [CRT0402-FZ-26R1GLF]	26.7 Ohm [CR0805-FX-26R7ELF]	261 Ohm [CRT0402-FZ-2610GLF]
26.1 kOhm [CR0402-FX-2612GLF]	26.1 Ohm [CRT0805-CX-26R1ELF]	26.7 Ohm [CR1206-FX-26R7ELF]	261 Ohm [CRT0603-BY-2610ELF]
26.1 kOhm [CR0603-FX-2612ELF]	26.7 kOhm [CAY16-2672F4LF]	261 kOhm [CR0402-FX-2613GLF]	267 kOhm [CR0402-FX-2673GLF]
26.1 kOhm [CR0805-FX-2612ELF]	26.7 kOhm [CR0402-FX-2672GLF]	261 kOhm [CR0603-FX-2613ELF]	267 kOhm [CR0603-FX-2673ELF]
26.1 kOhm [CR1206-FX-2612ELF]	26.7 kOhm [CR0603-FX-2672ELF]	261 kOhm [CR0805-FX-2613ELF]	267 kOhm [CR0805-FX-2673ELF]
26.1 kOhm [CRT0603-FZ-2612ELF]	26.7 kOhm [CR0805-FX-2672ELF]	261 kOhm [CR1206-FX-2613ELF]	267 kOhm [CR1206-FX-2673ELF]
26.1 kOhm [CRT0805-BY-2612ELF]	26.7 kOhm [CR1206-FX-2672ELF]	261 kOhm [CRT0805-CX-2613ELF]	267 kOhm [CRM2512-FX-2673ELF]
26.1 Ohm [CR0402-FX-26R1GLF]	26.7 kOhm [CRT0805-BY-2672ELF]	261 Ohm [CAY16-2610F4LF]	267 Ohm [CAY16-2670F4LF]
26.1 Ohm [CR0603-FX-26R1ELF]			

Multisim 14.1 Base Edition Components

267 Ohm [CR0402-FX-2670GLF]	27 kOhm [4306R-102-273LF]	27 kOhm [4420P-2-273]	27 kOhm [4610M-101-273LF]
267 Ohm [CR0603-FX-2670ELF]	27 kOhm [4308H-101-273]	27 kOhm [4420P-T02-273]	27 kOhm [4610X-101-273LF]
267 Ohm [CR0805-FX-2670ELF]	27 kOhm [4308H-101-273LF]	27 kOhm [4604X-101-273LF]	27 kOhm [4610X-102-273LF]
267 Ohm [CR1206-FX-2670ELF]	27 kOhm [4308R-101-273]	27 kOhm [4604X-102-273LF]	27 kOhm [4611X-101-273LF]
27 kOhm [4114R-1-273]	27 kOhm [4308R-101-273LF]	27 kOhm [4605X-101-273LF]	27 kOhm [4814P-T01-273]
27 kOhm [4114R-1-273LF]	27 kOhm [4308R-102-273]	27 kOhm [4606X-101-273LF]	27 kOhm [4814P-T01-273LF]
27 kOhm [4114R-2-273]	27 kOhm [4308R-102-273LF]	27 kOhm [4606X-102-273LF]	27 kOhm [4816P-1-273]
27 kOhm [4116R-1-273]	27 kOhm [4309R-101-273]	27 kOhm [4607M-101-273LF]	27 kOhm [4816P-1-273F]
27 kOhm [4116R-1-273LF]	27 kOhm [4309R-101-273LF]	27 kOhm [4607X-101-273LF]	27 kOhm [4816P-1-273LF]
27 kOhm [4116R-2-273]	27 kOhm [4310M-101-273]	27 kOhm [4608H-102-273LF]	27 kOhm [4816P-2-273]
27 kOhm [4116R-2-273LF]	27 kOhm [4310M-101-273LF]	27 kOhm [4608X-101-273LF]	27 kOhm [4816P-2-273LF]
27 kOhm [4306M-101-273]	27 kOhm [4310R-101-273]	27 kOhm [4608X-102-273LF]	27 kOhm [4816P-T01-273]
27 kOhm [4306R-101-273]	27 kOhm [4310R-101-273LF]	27 kOhm [4608X-AP2-273LF]	27 kOhm [4816P-T01-273LF]
27 kOhm [4306R-101-273LF]	27 kOhm [4310R-102-273]	27 kOhm [4609X-101-273LF]	27 kOhm [4816P-T02-273]
27 kOhm [4306R-102-273]	27 kOhm [4310R-102-273LF]	27 kOhm [4609X-AP1-273LF]	27 kOhm [4816P-T02-273LF]

Multisim 14.1 Base Edition Components

27 kOhm [4820P-2-273F]	27 kOhm [CR0603-JW-273ELF]	27 mOhm [PWR2615WR027JE]	27 nF [C0603C273K3RACTU]
27 kOhm [4820P-2-273LF]	27 kOhm [CR0805-FX-2702ELF]	27 mOhm [PWR4525WR027J]	27 nF [C0603C273K4RACTU]
27 kOhm [CAT16-2702F4LF]	27 kOhm [CR0805-FX-2702GLF]	27 mOhm [PWR4525WR027JE]	27 nF [C0603C273K5RACTU]
27 kOhm [CAT16-273J2LF]	27 kOhm [CR0805-JW-273ELF]	27 mOhm [PWR6327WR027J]	27 nF [C0805C273K1RACTU]
27 kOhm [CAT16-273J4LF]	27 kOhm [CR1206-FX-2702ELF]	27 mOhm [PWR6327WR027JE]	27 nF [C0805C273K2RACTU]
27 kOhm [CAT25-273JALF]	27 kOhm [CR1206-JW-273ELF]	27 nF [C0402C273K3RACTU]	27 nF [C0805C273K3HACTU]
27 kOhm [CAY10-273J4LF]	27 kOhm [CR2512-JW-273ELF]	27 nF [C0402C273K4RACTU]	27 nF [C0805C273K3RACTU]
27 kOhm [CAY16-2702F4LF]	27 kOhm [CRT0805-BY-2702ELF]	27 nF [C0402C273K8PACTU]	27 nF [C0805C273K4RACTU]
27 kOhm [CAY16-273J4LF]	27 mF [C0402C279K5GACTU]	27 nF [C0402C273K8RACTU]	27 nF [C0805C273K5RACTU]
27 kOhm [CAY16-273J8LF]	27 mF [C0805C279KBGACTU]	27 nF [C0402C273K9PACTU]	27 nF [C0805C273K8RACTU]
27 kOhm [CR0201-FW-2702GLF]	27 mOhm [PWR1913WR027J]	27 nF [C0402C273K9RACTU]	27 nF [C0805C273M5UACTU]
27 kOhm [CR0402-FX-2702GLF]	27 mOhm [PWR1913WR027JE]	27 nF [C0603C273K1RACTU]	
27 kOhm [CR0402-JW-273GLF]			
27 kOhm [CR0603-FX-2702ELF]			
27 kOhm [CR0603-FX-2702GLF]			

Multisim 14.1 Base Edition Components

27 nF [C0805F273K1RACT U]	27 nF [C1210C273K1HACT U]	27 nF [C1812C273K5HACT U]	27 Ohm [4114R-1- 270]
27 nF [C0805F273K3RACT U]	27 nF [C1210C273K1RACT U]	27 nF [C1825C273K1GACT U]	27 Ohm [4114R-1- 270LF]
27 nF [C0805F273K4RACT U]	27 nF [C1210C273K2RACT U]	27 nF [C1825C273K5GACT U]	27 Ohm [4114R-2- 270]
27 nF [C0805F273K5RACT U]	27 nF [C1210C273K3GACT U]	27 nF [C2220C273K1GACT U]	27 Ohm [4116R-1- 270LF]
27 nF [C1206C273K1HACT U]	27 nF [C1210C273K3HACT U]	27 nF [C2220C273K2GACT U]	27 Ohm [4116R-2- 270]
27 nF [C1206C273K1RACT U]	27 nF [C1210C273K5GACT U]	27 nF [GMC5.7272K250J3 1TR12]	27 Ohm [4306H- 102-270]
27 nF [C1206C273K3HACT U]	27 nF [C1210C273K5HACT U]	27 nF [GMC5.7273K50J31 TR12]	27 Ohm [4306R- 101-270]
27 nF [C1206C273K5HACT U]	27 nF [C1210C273K5RACT U]	27 nF [GMC7.3272K250K3 1TR12]	27 Ohm [4306R- 101-270LF]
27 nF [C1206C273K5RACT U]	27 nF [C1210C273KARACT U]	27 nF [GMC7.3272K63K31 TR12]	27 Ohm [4306R- 102-270]
27 nF [C1206C273KARACT U]	27 nF [C1812C273K1HACT U]	27 nF [GMC7.3273K63K31 TR12]	27 Ohm [4308R- 101-270]
27 nF [C1210C273K1GACT U]	27 nF [C1812C273K1RACT U]	27 nF [MMC5.7273K100J 31TR12]	27 Ohm [4308R- 101-270LF]
			27 Ohm [4310R- 101-270]

Multisim 14.1 Base Edition Components

27 Ohm [4310R-101-270LF]	27 Ohm [4610X-102-270LF]	27 Ohm [CAT16-270J4GLF]	27 Ohm [CR0805-FX-27R0ELF]
27 Ohm [4310R-102-270]	27 Ohm [4814P-1-270]	27 Ohm [CAT16-270J4LF]	27 Ohm [CR0805-JW-270ELF]
27 Ohm [4310R-102-270LF]	27 Ohm [4814P-T01-270]	27 Ohm [CAT16-270J8LF]	27 Ohm [CR1206-FX-27R0ELF]
27 Ohm [4416P-1-270]	27 Ohm [4816P-1-270]	27 Ohm [CAT16-27R0F4LF]	27 Ohm [CR1206-JW-270ELF]
27 Ohm [4416P-T01-270]	27 Ohm [4816P-1-270LF]	27 Ohm [CAT16-27R0F8LF]	27 Ohm [CR2010-JW-270ELF]
27 Ohm [4420P-1-270]	27 Ohm [4816P-2-270]	27 Ohm [CAT25-270JALF]	27 Ohm [CR2512-FX-27R0ELF]
27 Ohm [4420P-T01-270]	27 Ohm [4816P-2-270LF]	27 Ohm [CAY10-270J4LF]	27 Ohm [CR2512-JW-270ELF]
27 Ohm [4606X-101-270LF]	27 Ohm [4816P-T01-270]	27 Ohm [CAY16-270J4LF]	27 Ohm [CRM1206-JW-270ELF]
27 Ohm [4606X-102-270LF]	27 Ohm [4816P-T01-270LF]	27 Ohm [CAY16-270J8LF]	27 Ohm [FW20A27R0JA]
27 Ohm [4608H-102-270LF]	27 Ohm [4816P-T02-270]	27 Ohm [CAY16-27R0F4LF]	27 Ohm [PWR163S-25-27R0F]
27 Ohm [4608X-101-270LF]	27 Ohm [4816P-T02-270LF]	27 Ohm [CR0201-JW-270GLF]	27 Ohm [PWR163S-25-27R0FE]
27 Ohm [4608X-102-270LF]	27 Ohm [4820P-1-270]	27 Ohm [CR0402-FX-27R0GLF]	27 Ohm [PWR163S-25-27R0J]
27 Ohm [4608X-AP1-270LF]	27 Ohm [4820P-T01-270]	27 Ohm [CR0402-JW-270GLF]	27 Ohm [PWR220T-20-27R0F]
27 Ohm [4609X-101-270LF]	27 Ohm [4820P-T01-270LF]	27 Ohm [CR0603-FX-27R0ELF]	
27 Ohm [4610X-101-270LF]	27 Ohm [CAT10-270J4LF]	27 Ohm [CR0603-JW-270ELF]	

Multisim 14.1 Base Edition Components

27 Ohm [PWR220T-20- 27R0J]	27 pF [C0402C270K5GACT U]	27 pF [C1206C270K2GACT U]	27 uF [EEHZA1V270P] 27 uH [SDE0403A- 270M]
27 Ohm [PWR220T-35- 27R0J]	27 pF [C0402C270K8GACT U]	27 pF [C1206C270K5GACT U]	27 uH [SDE0604A- 270M]
27 Ohm [PWR221T-30- 27R0F]	27 pF [C0603C270K1GACT U]	27 pF [C1206C270KBGAC TU]	27 uH [SDE0805A- 270M]
27 Ohm [PWR263S-20- 27R0F]	27 pF [C0603C270K2GACT U]	27 pF [C1210C270KBGAC TU]	27 uH [SDE1006A- 270M]
27 Ohm [PWR263S-20- 27R0J]	27 pF [C0603C270K5GACT U]	27 pF [C1812C270KBGAC TU]	27 uH [SDR0302- 270ML]
27 Ohm [PWR263S-35- 27R0F]	27 pF [C0805C270K1GACT U]	27 pF [C1812C270KHGAC TU]	27 uH [SDR0503- 270ML]
27 Ohm [PWR263S-35- 27R0FE]	27 pF [C0805C270K2GACT U]	27 pF [C1825C270KBGAC TU]	27 uH [SDR0603- 270ML]
27 Ohm [PWR263S-35- 27R0J]	27 pF [C0805C270K5GACT U]	27 pF [C2220C270KBGAC TU]	27 uH [SDR0604- 270YL]
27 pF [C0201C270K3GACT U]	27 pF [C0805C270KBGAC TU]	27 pF [C2225C270KBGAC TU]	27 uH [SDR0703- 270KL]
27 pF [C0402C270K3GACT U]	27 pF [C0805C270KDGAC TU]	27 pF [CA064C270K5GAC TU]	27 uH [SDR0805- 270KL]
27 pF [C0402C270K4GACT U]	27 pF [C1206C270K1GACT U]	27 pF [CA064C270K8GAC TU]	27 uH [SDR0906- 270KL]
			27 uH [SDR1006- 270KL]
			27 uH [SDR1105- 270ML]

Multisim 14.1 Base Edition Components

27 uH [SDR1307-270ML]	27 uH [SRR1208-270ML]	27 uH [SRU1038-270Y]	270 kOhm [4114R-1-274]
27 uH [SDR1307A-270M]	27 uH [SRR1210-270M]	27 uH [SRU8043-270Y]	270 kOhm [4114R-1-274LF]
27 uH [SRN5040-270M]	27 uH [SRR1210A-270M]	27.4 kOhm [CR0402-FX-2742GLF]	270 kOhm [4116R-1-274]
27 uH [SRP6540-270M]	27 uH [SRR1240-270M]	27.4 kOhm [CR0603-FX-2742ELF]	270 kOhm [4116R-1-274LF]
27 uH [SRR0735A-270M]	27 uH [SRR1260-270M]	27.4 kOhm [CR0805-FX-2742ELF]	270 kOhm [4116R-2-274]
27 uH [SRR0745A-270M]	27 uH [SRR1260A-270M]	27.4 kOhm [CR1206-FX-2742ELF]	270 kOhm [4306H-101-274]
27 uH [SRR0804-270Y]	27 uH [SRR1280-270M]	27.4 kOhm [CAY16-27R4F4LF]	270 kOhm [4306H-102-274]
27 uH [SRR0805-270Y]	27 uH [SRR4018-270Y]	27.4 kOhm [CRT0805-BY-2742ELF]	270 kOhm [4306R-101-274]
27 uH [SRR0905-270M]	27 uH [SRR4028-270Y]	27.4 Ohm [CR0402-FX-27R4GLF]	270 kOhm [4306R-102-274]
27 uH [SRR0906-270ML]	27 uH [SRR5018-270Y]	27.4 Ohm [CR0603-FX-27R4ELF]	270 kOhm [4306R-102-274LF]
27 uH [SRR0908-270ML]	27 uH [SRR5028-270Y]	27.4 Ohm [CR0805-FX-27R4ELF]	270 kOhm [4308R-101-274]
27 uH [SRR1003-270M]	27 uH [SRR6028-270Y]	27.4 Ohm [CR1206-FX-27R4ELF]	270 kOhm [4308R-101-274LF]
27 uH [SRR1005-270Y]	27 uH [SRR6038-270Y]	27.4 Ohm [CRM1206-FX-27R4ELF]	270 kOhm [4308R-102-274]
27 uH [SRR1205-270ML]	27 uH [SRR6040A-270M]		
27 uH [SRR1206-270ML]	27 uH [SRR7045-270M]		

Multisim 14.1 Base Edition Components

270 kOhm [4310R-101-274]	270 kOhm [4609X-101-274LF]	270 kOhm [CAY16-274J4LF]	270 mOhm [CRL0603-FW-R270ELF]
270 kOhm [4310R-101-274LF]	270 kOhm [4610X-101-274LF]	270 kOhm [CAY16-274J8LF]	270 mOhm [CRL0603-JW-R270ELF]
270 kOhm [4310R-102-274]	270 kOhm [4610X-102-274LF]	270 kOhm [CR0402-FX-2703GLF]	270 mOhm [CRL0805-FW-R270ELF]
270 kOhm [4310R-102-274LF]	270 kOhm [4814P-1-274]	270 kOhm [CR0603-FX-2703ELF]	270 mOhm [CRL0805-JW-R270ELF]
270 kOhm [4416P-1-274]	270 kOhm [4816P-1-274]	270 kOhm [CR0603-JW-274ELF]	270 mOhm [CRL1206-FW-R270ELF]
270 kOhm [4416P-2-274]	270 kOhm [4816P-1-274LF]	270 kOhm [CR0603-JW-274GLF]	270 mOhm [CRL1206-JW-R270ELF]
270 kOhm [4416P-T01-274]	270 kOhm [4816P-2-274]	270 kOhm [CR0805-FX-2703ELF]	270 mOhm [CRL2010-FW-R270ELF]
270 kOhm [4416P-T02-274]	270 kOhm [4816P-2-274LF]	270 kOhm [CR0805-JW-274ELF]	270 mOhm [CRL2010-JW-R270ELF]
270 kOhm [4604M-101-274LF]	270 kOhm [4816P-T01-274]	270 kOhm [CR0805-JW-274GLF]	270 mOhm [CRL2512-FW-R270ELF]
270 kOhm [4604X-102-274LF]	270 kOhm [4816P-T01-274LF]	270 kOhm [CR1206-FX-2703ELF]	270 mOhm [CRM2010-FX-R270ELF]
270 kOhm [4606X-101-274LF]	270 kOhm [4816P-T02-274]	270 kOhm [CR1206-JW-274ELF]	270 mOhm [CRM2512-FX-R270ELF]
270 kOhm [4606X-102-274LF]	270 kOhm [4816P-T02-274LF]	270 kOhm [CRM2512-JW-274ELF]	
270 kOhm [4608X-101-274LF]	270 kOhm [CAT16-2703F4LF]		
270 kOhm [4608X-102-274LF]	270 kOhm [CAT16-274J4LF]		
270 kOhm [4609H-101-274LF]	270 kOhm [CAT25-274JALF]		

Multisim 14.1 Base Edition Components

270 mOhm [PWR220T-20- R270F]	270 nF [C0805C274K4RACT U]	270 nF [C1210C274K5RACT U]	270 nF [C1812F274K3RACT U]
270 mOhm [PWR220T-35- R270F]	270 nF [C0805C274K8RACT U]	270 nF [C1210C274M5UAC TU]	270 nF [C1812F274K5RACT U]
270 mOhm [PWR263S-35- R270F]	270 nF [C1206C274K1RACT U]	270 nF [C1210F274K1RACT U]	270 nF [C1825C274K1RACT U]
270 mOhm [PWR263S-35- R270FE]	270 nF [C1206C274K3RACT U]	270 nF [C1210F274K3RACT U]	270 nF [C1825C274K5RACT U]
270 nF [C0603C274K4PACT U]	270 nF [C1206C274K4RACT U]	270 nF [C1210F274K4RACT U]	270 nF [C2220C274K1GACT U]
270 nF [C0603C274K4RACT U]	270 nF [C1206C274K5RACT U]	270 nF [C1210F274K5RACT U]	270 nF [C2220C274K5GACT U]
270 nF [C0603C274K8PACT U]	270 nF [C1206F274K3RACT U]	270 nF [C1812C274K1RACT U]	270 nF [C2220C274K5RACT U]
270 nF [C0603C274K8RACT U]	270 nF [C1206F274K4RACT U]	270 nF [C1812C274K5RACT U]	270 nF [C2225C274K1RACT U]
270 nF [C0603C274K9PACT U]	270 nF [C1206F274K5RACT U]	270 nF [C1812C274KARACT U]	270 nF [C2225C274K2RACT U]
270 nF [C0603C274K9RACT U]	270 nF [C1210C274K1RACT U]	270 nF [C1812F274K1RACT U]	270 nF [C2225C274K5RACT U]
270 nF [C0805C274K3RACT U]	270 nF [C1210C274K3RACT U]	270 nF [C1812F274K2RACT U]	270 nF [GMC7.3274K63K35 TR12]

Multisim 14.1 Base Edition Components

270 nF [MDC10274K100A5 2P3TUBE]	270 nF [MDK15274K50B53 P3TUBE]	270 Ohm [4116R-2- 271LF]	270 Ohm [4310M- 102-271]
270 nF [MDC10274K250A5 2P3TUBE]	270 nF [MDS15274K400B5 3P3TUBE]	270 Ohm [4304M- 102-271]	270 Ohm [4310R- 101-271]
270 nF [MDC10274K400A5 7P7TUBE]	270 nF [MDS15274K50B53 P3TUBE]	270 Ohm [4306M- 101-271]	270 Ohm [4310R- 101-271LF]
270 nF [MDC10274K400A5 7P8TUBE]	270 nF [MMC16.5274K400 C31TR24]	270 Ohm [4306R- 101-271LF]	270 Ohm [4310R- 102-271LF]
270 nF [MDC10274K50A52 P3TUBE]	270 nF [MMC7.3274K63K3 5TR12]	270 Ohm [4306R- 102-271]	270 Ohm [4416P-2- 271]
270 nF [MDC15274K100B5 3P3TUBE]	270 nH [SRP1038A- R27M]	270 Ohm [4306R- 102-271LF]	270 Ohm [4416P- T01-271]
270 nF [MDC15274K250B5 3P3TUBE]	270 Ohm [4114R-1- 271]	270 Ohm [4308M- 102-271]	270 Ohm [4416P- T02-271]
270 nF [MDC15274K400B5 3P3TUBE]	270 Ohm [4114R-1- 271LF]	270 Ohm [4308R- 101-271]	270 Ohm [4420P-1- 271]
270 nF [MDC15274K50B53 P3TUBE]	270 Ohm [4114R-2- 271]	270 Ohm [4308R- 101-271LF]	270 Ohm [4420P-2- 271]
270 nF [MDK15274K100B5 3P3TUBE]	270 Ohm [4114R-2- 271LF]	270 Ohm [4308R- 102-271]	270 Ohm [4420P-2- 271LF]
270 nF [MDK15274K50B53 P3TUBE]	270 Ohm [4116R-1- 271]	270 Ohm [4308R- 102-271LF]	270 Ohm [4420P- T01-271]
270 nF [MDK15274K100B5 3P3TUBE]	270 Ohm [4116R-1- 271LF]	270 Ohm [4309R- 101-271]	270 Ohm [4420P- T02-271]
270 nF [MDK15274K400B5 3P3TUBE]	270 Ohm [4116R-2- 271]	270 Ohm [4309R- 101-271LF]	270 Ohm [4420P- T04-271]
270 nF [MDK15274K400B5 3P3TUBE]	270 Ohm [4116R-2- 271]	270 Ohm [4310M- 101-271]	270 Ohm [4604M- 101-271LF]

Multisim 14.1 Base Edition Components

270 Ohm [4604X-101-271LF]	270 Ohm [4610X-102-271LF]	270 Ohm [4816P-T01-271]	270 Ohm [CAY16-271J2LF]
270 Ohm [4604X-102-271LF]	270 Ohm [4611X-101-271LF]	270 Ohm [4816P-T01-271LF]	270 Ohm [CAY16-271J4LF]
270 Ohm [4605X-101-271LF]	270 Ohm [4612X-102-271LF]	270 Ohm [4816P-T02-271]	270 Ohm [CAY16-271J8LF]
270 Ohm [4606X-101-271LF]	270 Ohm [4614X-102-271LF]	270 Ohm [4816P-T02-271LF]	270 Ohm [CR0402-FX-2700GLF]
270 Ohm [4606X-102-271LF]	270 Ohm [4814P-1-271]	270 Ohm [4820P-1-271]	270 Ohm [CR0402-JW-271GLF]
270 Ohm [4606X-AP1-271LF]	270 Ohm [4814P-1-271LF]	270 Ohm [4820P-2-271]	270 Ohm [CR0603-FX-2700ELF]
270 Ohm [4607X-101-271LF]	270 Ohm [4814P-2-271]	270 Ohm [4820P-T01-271]	270 Ohm [CR0603-FX-2700GLF]
270 Ohm [4608M-102-271LF]	270 Ohm [4814P-T01-271]	270 Ohm [4820P-T02-271]	270 Ohm [CR0603-JW-271ELF]
270 Ohm [4608X-101-271LF]	270 Ohm [4814P-T01-271LF]	270 Ohm [CAT10-271J4LF]	270 Ohm [CR0603-JW-271GLF]
270 Ohm [4608X-102-271LF]	270 Ohm [4814P-T02-271]	270 Ohm [CAT16-2700F4LF]	270 Ohm [CR0805-FX-2700ELF]
270 Ohm [4609H-101-271LF]	270 Ohm [4814P-T02-271LF]	270 Ohm [CAT16-271J4LF]	270 Ohm [CR0805-FX-2700GLF]
270 Ohm [4609M-101-271LF]	270 Ohm [4816P-1-271]	270 Ohm [CAT16-271J8LF]	270 Ohm [CR0805-JW-271ELF]
270 Ohm [4609X-101-271LF]	270 Ohm [4816P-1-271LF]	270 Ohm [CAT25-271JALF]	270 Ohm [CR1206-FX-2700ELF]
270 Ohm [4610H-101-271LF]	270 Ohm [4816P-2-271]	270 Ohm [CAY10-271J4LF]	270 Ohm [CR1206-JW-271ELF]
270 Ohm [4610X-101-271LF]	270 Ohm [4816P-2-271LF]	270 Ohm [CAY16-2700F4LF]	270 Ohm [CR2512-JW-271ELF]

Multisim 14.1 Base Edition Components

270 Ohm [CRM1206-FX- 2700ELF]	270 pF [C0402C271K5RACT U]	270 pF [C0805C271K2GACT U]	270 pF [C1825C271KBGAC TU]
270 Ohm [CRM2512-FX- 2700ELF]	270 pF [C0402C271K8RACT U]	270 pF [C0805C271K2RACT U]	270 pF [C2220C271KBGAC TU]
270 Ohm [CRM2512-JW- 271ELF]	270 pF [C0603C271K1RACT U]	270 pF [C0805C271K4RACT U]	270 pF [C2225C271KBGAC TU]
270 Ohm [PWR263S-35- 2700J]	270 pF [C0603C271K2RACT U]	270 pF [C0805C271K5GACT U]	270 uF [10SVPC270M]
270 Ohm [PWR5322W2700FE]	270 pF [C0603C271K3RACT U]	270 pF [C0805C271K5RACT U]	270 uF [16SEPC270M]
270 pF [C0402C271K1HACT U]	270 pF [C0603C271K4GACT U]	270 pF [C1206C271K1GACT U]	270 uF [16SVPC270M]
270 pF [C0402C271K3HACT U]	270 pF [C0603C271K4RACT U]	270 pF [C1206C271K2GACT U]	270 uF [2TPSF270M6E]
270 pF [C0402C271K3RACT U]	270 pF [C0603C271K5GACT U]	270 pF [C1206C271K5GACT U]	270 uF [2TPSF270M9G]
270 pF [C0402C271K4RACT U]	270 pF [C0603C271K5RACT U]	270 pF [C1206C271KBGAC TU]	270 uF [A700X277M002AT E010]
270 pF [C0402C271K5GACT U]	270 pF [C0805C271K1GACT U]	270 pF [C1210C271KBGAC TU]	270 uF [A700X277M002AT E015]
270 pF [C0402C271K5HACT U]	270 pF [C0805C271K1RACT U]	270 pF [C1812C271KBGAC TU]	270 uF [A700X277M004AT E010]
			270 uF [A700X277M004AT E015]

Multisim 14.1 Base Edition Components

270 uF [EEFCX0D271XR]	270 uH [SDR0403- 271KL]	270 uH [SRR0906- 271YL]	274 kOhm [CR0402-FX- 2743GLF]
270 uF [EEFCX0G271R]	270 uH [SDR0503- 271KL]	270 uH [SRR0908- 271YL]	274 kOhm [CR0603-FX- 2743ELF]
270 uF [EEFLT0E271R]	270 uH [SDR0603- 271KL]	270 uH [SRR1003- 271Y]	274 kOhm [CR0805-FX- 2743ELF]
270 uF [EEFST0E271R]	270 uH [SDR0604- 271KL]	270 uH [SRR1005- 271K]	274 kOhm [CR1206-FX- 2743ELF]
270 uF [EEFSX0D271E4]	270 uH [SDR0703- 271KL]	270 uH [SRR1205- 271KL]	274 kOhm [CR1206-FX- 2743ELF]
270 uF [EEFSX0D271ER]	270 uH [SDR0805- 271KL]	270 uH [SRR1206- 271KL]	274 kOhm [CRT0603-BY- 2743ELF]
270 uF [EEFSX0D271XE]	270 uH [SDR0906- 271KL]	270 uH [SRR1208- 271KL]	274 Ohm [CAY16- 2740F4LF]
270 uF [EEFSX0E271E7]	270 uH [SDR1006- 271KL]	270 uH [SRR1210- 271M]	274 Ohm [CR0402- FX-2740GLF]
270 uF [EEFSX0G271ER]	270 uH [SDR1307- 271KL]	270 uH [SRR1210A- 271M]	274 Ohm [CR0603- FX-2740ELF]
270 uF [EEHZA1V271P]	270 uH [SDR1307A-271K]	270 uH [SRR1240- 271K]	274 Ohm [CR0805- FX-2740ELF]
270 uF [EEHZC1V271P]	270 uH [SRR0735A- 271M]	270 uH [SRR1260- 271K]	274 Ohm [CR1206- FX-2740ELF]
270 uF [ETPSF270M6E]	270 uH [SRR0745A- 271M]	270 uH [SRR1260A- 271K]	274 Ohm [CRT0402-FZ- 2740GLF]
270 uH [SDE0805A- 271K]	270 uH [SRR0804- 271K]	270 uH [SRR1280- 271K]	28 kOhm [CR0402- FX-2802GLF]
270 uH [SDE1006A- 271K]	270 uH [SRR0805- 271K]	270 uH [SRR4028- 271Y]	28 kOhm [CR0603- FX-2802ELF]
270 uH [SDR0302- 271KL]	270 uH [SRR0905- 271K]	270 uH [SRR7045- 271M]	

Multisim 14.1 Base Edition Components

28 kOhm [CR0805-FX-2802ELF]	28.7 kOhm [CRT0805-BY-2872ELF]	280 Ohm [CRT0805-BY-2800ELF]	287 Ohm [CR1206-FX-2870ELF]
28 kOhm [CR1206-FX-2802ELF]	28.7 Ohm [CR0603-FX-28R7ELF]	282834-2	287 Ohm [CRM2512-FX-2870ELF]
28 kOhm [CR1206-FX-2802ELFF]	28.7 Ohm [CR0805-FX-28R7ELF]	282834-4	287 Ohm [CRT0402-FZ-2870GLF]
28 kOhm [CRT0805-FY-2802ELF]	28.7 Ohm [CR1206-FX-28R7ELF]	282834-5	287 Ohm [CRT0402-FZ-2870GLF]
		282834-8	287 Ohm [CRT1206-BY-2870ELF]
28 Ohm [CAY16-28R0F4LF]	28.7 Ohm [CRT0402-FZ-28R7GLF]	284258	28V_7.5W
28 Ohm [CR0402-FX-28R0GLF]	280 kOhm [CR0402-FX-2803GLF]	287 kOhm [CAT16-2873F4LF]	29 kOhm [4116R-1-293]
28 Ohm [CR0603-FX-28R0ELF]		287 kOhm [CR0402-FX-2873GLF]	29 kOhm [4116R-1-293LF]
28 Ohm [CR0805-FX-28R0ELF]	280 kOhm [CR0603-FX-2803ELF]	287 kOhm [CR0603-FX-2873ELF]	29.4 kOhm [CR0402-FX-2942GLF]
28 Ohm [CR1206-FX-28R0ELF]	280 kOhm [CR0805-FX-2803ELF]	287 kOhm [CR0805-FX-2873ELF]	29.4 kOhm [CR0603-FX-2942ELF]
28.7 kOhm [CR0402-FX-2872GLF]	280 kOhm [CR1206-FX-2803ELF]	287 kOhm [CR1206-FX-2873ELF]	29.4 kOhm [CR0805-FX-2942ELF]
28.7 kOhm [CR0603-FX-2872ELF]	280 Ohm [CR0402-FX-2800GLF]	287 Ohm [CR0201-FW-2870GLF]	29.4 kOhm [CR1206-FX-2942ELF]
28.7 kOhm [CR0805-FX-2872ELF]	280 Ohm [CR0603-FX-2800ELF]	287 Ohm [CR0402-FX-2870GLF]	
28.7 kOhm [CR1206-FX-2872ELF]	280 Ohm [CR0805-FX-2800ELF]	287 Ohm [CR0603-FX-2870ELF]	29.4 kOhm [CRT0805-BY-2942ELF]
	280 Ohm [CR1206-FX-2800ELF]	287 Ohm [CR0805-FX-2870ELF]	29.4 Ohm [CR0402-FX-29R4GLF]

Multisim 14.1 Base Edition Components

29.4 Ohm [CR0603-FX-29R4ELF]	294 kOhm [CR0603-FX-2943ELF]	2N2579	2N3668
29.4 Ohm [CR0805-FX-29R4ELF]	294 kOhm [CR0805-FX-2943ELF]	2N2608	2N3669
29.4 Ohm [CR1206-FX-29R4ELF]	294 kOhm [CR1206-FX-2943ELF]	2N2609	2N3670
290 mOhm [PWR1913WR290J]	294 Ohm [CR0402-FX-2940GLF]	2N2712	2N3684
290 mOhm [PWR1913WR290JE]	294 Ohm [CR0603-FX-2940ELF]	2N2714	2N3685
290 mOhm [PWR2615WR290J]	294 Ohm [CR0603-FX-2940GLF]	2N2923	2N3686
290 mOhm [PWR2615WR290JE]	294 Ohm [CR0805-FX-2940ELF]	2N2924	2N3687
290 mOhm [PWR4525WR290J]	294 Ohm [CR1206-FX-2940ELF]	2N2925	2N3702
290 mOhm [PWR4525WR290JE]	2A3	2N3055A	2N3703
290 mOhm [PWR6327WR290J]	2K8RAM	2N3055AG	2N3707
290 mOhm [PWR6327WR290JE]	2N1599	2N3055G	2N3711
292303-1	2N2222A	2N3370	2N3771G
292304-1	2N2573	2N3390	2N3772G
294 kOhm [CR0402-FX-2943GLF]	2N2574	2N3391	2N3773G
	2N2575	2N3391A	2N3821
	2N2576	2N3392	2N3822
	2N2577	2N3393	2N3823
	2N2578	2N3394	2N3824
		2N3414	2N3858A
		2N3415	2N3859
		2N3416	2N3859A
		2N3417	2N3860
		2N3442G	2N3870
		2N3458	2N3871
		2N3459	2N3872

Multisim 14.1 Base Edition Components

2N3873	2N4058	2N4186	2N4381
2N3896	2N4061	2N4187	2N4391
2N3897	2N4062	2N4188	2N4392
2N3898	2N4084	2N4189	2N4393
2N3899	2N4091	2N4190	2N4400
2N3903	2N4092	2N4199	2N4401
2N3904	2N4093	2N4200	2N4402
2N3904G	2N4117A	2N4201	2N4403
2N3905	2N4118A	2N4202	2N4409
2N3906	2N4119A	2N4203	2N4410
2N3906G	2N4123	2N4204	2N4416
2N3921	2N4124	2N4220	2N4416A
2N3922	2N4125	2N4220A	2N4424
2N3954	2N4126	2N4221	2N4441
2N3954A	2N4167	2N4221A	2N4442
2N3955	2N4168	2N4222	2N4443
2N3955A	2N4169	2N4222A	2N4444
2N3956	2N4170	2N4223	2N4856
2N3957	2N4171	2N4286	2N4856A
2N3958	2N4172	2N4289	2N4857
2N3966	2N4173	2N4291	2N4857A
2N3967	2N4174	2N4338	2N4858
2N3970	2N4183	2N4339	2N4858A
2N3971	2N4184	2N4340	2N4859
2N3972	2N4185	2N4341	2N4859A

Multisim 14.1 Base Edition Components

2N4860	2N5087	2N5227	2N5515
2N4860A	2N5088	2N5232	2N5516
2N4861	2N5089	2N5232A	2N5517
2N4861A	2N5103	2N5302G	2N5518
2N4918G	2N5105	2N5354	2N5519
2N4919G	2N5114	2N5355	2N5520
2N4920G	2N5115	2N5358	2N5521
2N4921G	2N5116	2N5365	2N5522
2N4922G	2N5168	2N5366	2N5523
2N4923G	2N5169	2N5397	2N5524
2N5018	2N5170	2N5398	2N5545
2N5019	2N5171	2N5400	2N5550
2N5020	2N5172	2N5401	2N5550G
2N5021	2N5191G	2N5432	2N5550RLRPG
2N5038G	2N5192G	2N5433	2N5551
2N5045	2N5194G	2N5434	2N5556
2N5046	2N5195G	2N5444	2N5557
2N5047	2N5196	2N5445	2N5558
2N5060	2N5197	2N5446	2N5564
2N5061	2N5199	2N5447	2N5565
2N5062	2N5209	2N5452	2N5566
2N5063	2N5210	2N5454	2N5567
2N5064	2N5223	2N5484	2N5568
2N5078	2N5224	2N5485	2N5571
2N5086	2N5226	2N5486	2N5572

Multisim 14.1 Base Edition Components

2N5655G	2N6039G	2N6169	2N6396
2N5657G	2N6040G	2N6170	2N6397
2N5684G	2N6042G	2N6171	2N6398
2N5686G	2N6043G	2N6172	2N6399
2N5769	2N6045G	2N6173	2N6400
2N5771	2N6052G	2N6174	2N6401
2N5817	2N6071	2N6284G	2N6402
2N5830	2N6073BG	2N6286G	2N6403
2N5883G	2N6107G	2N6287G	2N6404
2N5884G	2N6109G	2N6288G	2N6405
2N5885G	2N6111G	2N6292G	2N6487G
2N5886G	2N6145	2N6338G	2N6488G
2N6027	2N6146	2N6341G	2N6490G
2N6027G	2N6147	2N6342	2N6491G
2N6027RL1G	2N6157	2N6343	2N6667G
2N6027RLRAG	2N6158	2N6344	2N6715
2N6028	2N6159	2N6345	2N6727
2N6028G	2N6160	2N6346	2N7000
2N6028RLRAG	2N6161	2N6347	2N7000G
2N6028RLRMG	2N6162	2N6348	2N7000RLRAG
2N6028RLRPG	2N6163	2N6349	2N7002
2N6034G	2N6164	2N6387G	2N7002BK
2N6035G	2N6165	2N6388G	2N7002BKM
2N6036G	2N6167	2N6394	2N7002BKMB
2N6038G	2N6168	2N6395	2N7002BKS

Multisim 14.1 Base Edition Components

2N7002BKT	2PA1774RM	2PC4617RM	2SA2126-E
2N7002BKV	2PA1774RMB	2PC4617RMB	2SA2126-H
2N7002BKW	2PA1774S	2PD1820AR	2SA2126-TL-E
2N7002CK	2PA1774SM	2PD1820AS	2SA2126-TL-H
2N7002DW	2PA1774SMB	2PD2150	2SA2205-E
2N7002E	2PB1219AQ	2PD601ARL	2SA2205-TL-E
2N7002ET1G	2PB1219AR	2PD601ART	2SA2210-1E
2N7002F	2PB1219AS	2PD601ARW	2SA2222SG
2N7002K	2PB1424	2PD601ASL	2SA733
2N7002LT1G	2PB709ARL	2PD601ASW	2SA952
2N7002LT3G	2PB709ART	2PD601BRL	2SA953
2N7002P	2PB709ARW	2PD601BSL	2SA954
2N7002PS	2PB709ASL	2PD602AQL	2SB1204S-E
2N7002PT	2PB709ASW	2PD602ARL	2SB1204S-TL-E
2N7002PV	2PB709BRL	2PD602ASL	2SB1205S-TL-E
2N7002PW	2PB709BSL	2SA1015	2SB1205T-TL-E
2P1S	2PB710ARL	2SA1020	2SC1815
2P2S	2PB710ASL	2SA1213	2SC2001
2PA1576Q	2PC4081Q	2SA1416S-TD-E	2SC2120
2PA1576R	2PC4081R	2SA1416T-TD-E	2SC2240
2PA1576S	2PC4081S	2SA1460	2SC2655
2PA1774Q	2PC4617Q	2SA1507S	2SC2786
2PA1774QM	2PC4617QM	2SA1507T	2SC2873
2PA1774QMB	2PC4617QMB	2SA1774G	2SC3332S
2PA1774R	2PC4617R	2SA1774T1G	2SC3332S-AA

Multisim 14.1 Base Edition Components

2SC3649S-TD-E	2SD1628G-TD-E	2SK3069	2SK3747-1E
2SC3649S-TD-H	2SD1628G-TD-H	2SK3070L	2SK3748
2SC3649T-TD-E	2SD1805F-E	2SK3070S	2SK3748-1E
2SC3649T-TD-H	2SD1805F-TL-E	2SK30ATM	2SK3820-DL-E
2SC3733	2SD1805G-E	2SK3133	2SK3820-E
2SC4617G	2SD1805G-TL-E	2SK3134	2SK536-TB-E
2SC4617T1G	2SD1815S-E	2SK3135	2V7002LT1G
2SC5566-TD-E	2SD1815S-TL-E	2SK3136	2V7002LT3G
2SC5658M3T5G	2SD1815T-E	2SK3140	3 kOhm [4116R-1-302]
2SC5706-E	2SD1815T-TL-E	2SK3141	3 kOhm [4116R-1-302LF]
2SC5706-H	2SJ517	2SK3142	3 kOhm [4304H-102-302]
2SC5706-TL-E	2SJ652	2SK3203	3 kOhm [4304M-102-302]
2SC5706-TL-H	2SJ652-RA11	2SK3233	3 kOhm [4304M-102-302LF]
2SC5964-TD-E	2SJ661-E	2SK330	3 kOhm [4306H-101-302]
2SC5964-TD-H	2SJ665-DL-E	2SK3557-6-TB-E	3 kOhm [4306R-101-302]
2SC5994-TD-E	2SK117	2SK3557-7-TB-E	3 kOhm [4306R-101-302LF]
2SC6082	2SK170	2SK364	3 kOhm [4308R-102-302]
2SC6097-E	2SK192A	2SK366	3 kOhm [4310R-101-302]
2SC6097-TL-E	2SK208	2SK367	3 kOhm [4310R-101-302LF]
2SC6144SG	2SK209	2SK368	3 kOhm [4310R-101-302LF]
2SC945	2SK2394-6-TB-E	2SK3703	3 kOhm [4310R-101-302]
2SD1623S-TD-E	2SK2553L	2SK3704	3 kOhm [4310R-101-302]
2SD1623T-TD-E	2SK2553S	2SK3746	3 kOhm [4310R-101-302]
2SD1628F-TD-E	2SK2978	2SK3746-1E	3 kOhm [4310R-101-302]
2SD1628F-TD-H	2SK2980	2SK3747	

Multisim 14.1 Base Edition Components

3 kOhm [4310R-101-302LF]	3 kOhm [CR0603-JW-302ELF]	3 kOhm [PWR2615W3001FE]	3 nF [C0603C302K3HACTU]
3 kOhm [4607X-101-302LF]	3 kOhm [CR0805-FX-3001ELF]	3 kOhm [PWR2615W3001J]	3 nF [C0603C302K5HACTU]
3 kOhm [4610X-101-302LF]	3 kOhm [CR0805-FX-3001GLF]	3 kOhm [PWR2615W3001JE]	3 nF [C0805C302K1GACTU]
3 kOhm [4814P-1-302]	3 kOhm [CR0805-JW-302ELF]	3 kOhm [PWR263S-35-3001F]	3 nF [C0805C302K1HACTU]
3 kOhm [4814P-2-302]	3 kOhm [CR1206-FX-3001ELF]	3 kOhm [PWR4525W3001J]	3 nF [C0805C302K3GACTU]
3 kOhm [4814P-2-302LF]	3 kOhm [CR1206-JW-302ELF]	3 MOhm [4116R-1-305LF]	3 nF [C0805C302K3HACTU]
3 kOhm [4816P-1-302]	3 kOhm [CR2512-FX-3001ELF]	3 MOhm [CR0603-JW-305ELF]	3 nF [C0805C302K5HACTU]
3 kOhm [4816P-1-302LF]	3 kOhm [CR2512-JW-302ELF]	3 MOhm [CR0805-JW-305ELF]	3 nF [C1825C302KBGAC TU]
3 kOhm [CAT16-302J4LF]	3 kOhm [CRM2512-FX-3001ELF]	3 MOhm [CR1206-JW-305ELF]	3 nF [C2220C302KBGAC TU]
3 kOhm [CAT25-302JALF]	3 kOhm [CRM2512-JW-302ELF]	3 mOhm [CRE2512-FZ-R003E-2]	3 nF [C2225C302KBGAC TU]
3 kOhm [CAY10-302J4LF]	3 kOhm [CRT0603-FX-3001ELF]	3 mOhm [CRF2512-FX-R003ELF]	3 nF [CAT10-3R0J4LF]
3 kOhm [CAY16-302J4LF]	3 kOhm [CRT0805-BY-3001ELF]	3 mOhm [CRF2512-JX-R003ELF]	3 Ohm [CAT16-3R0J2LF]
3 kOhm [CR0402-FX-3001GLF]	3 kOhm [CRT1206-BY-3001ELF]	3 nF [C0603C302K1HACTU]	
3 kOhm [CR0402-JW-302GLF]	3 kOhm [PWR220T-35-3001J]		

Multisim 14.1 Base Edition Components

3 Ohm [CAT16-3R0J4LF]	3 Ohm [CRL0805-JW-3R00ELF]	3 Ohm [PWR2615W3R00F]	3 uH [SRR5028-3R0Y]
3 Ohm [CAY10-3R0J2LF]	3 Ohm [CRL1206-FW-3R00ELF]	3 Ohm [PWR2615W3R00F E]	3 uH [SRR6028-3R0Y]
3 Ohm [CAY10-3R0J4LF]	3 Ohm [CRL2010-FW-3R00ELF]	3 Ohm [PWR263S-20-3R00F]	3 uH [SRR6040A-3R0Y]
3 Ohm [CAY16-3R0J2LF]	3 Ohm [CRL2010-JW-3R00ELF]	3 Ohm [PWR263S-20-3R00FE]	3 uH [SRU1048-3R0Y]
3 Ohm [CAY16-3R0J4LF]	3 Ohm [CRL2512-FW-3R00ELF]	3 Ohm [PWR263S-20-3R00J]	3 uH [SRU1048A-3R0Y]
3 Ohm [CR0402-J/-3R0GLF]	3 Ohm [CRM2512-JW-3R0ELF]	3 Ohm [PWR263S-20-3R00JE]	3 uH [SRU2016-3R0Y]
3 Ohm [CR0603-J/-3R0ELF]	3 Ohm [CRT0805-DY-3R00ELF]	3 Ohm [PWR263S-35-3R00F]	3 uH [SRU3014-3R0Y]
3 Ohm [CR0603-J/-3R0GLF]	3 Ohm [CRT0805-FZ-3R00ELF]	3 Ohm [PWR263S-35-3R00FE]	3.01 kOhm [CAY16-3011F4LF]
3 Ohm [CR0805-J/-3R0ELF]	3 Ohm [PWR163S-25-3R00F]	3 Ohm [PWR263S-35-3R00J]	3.01 kOhm [CR0402-FX-3011GLF]
3 Ohm [CR1206-J/-3R0ELF]	3 Ohm [PWR163S-25-3R00FE]	3 Ohm [PWR263S-35-3R00JE]	3.01 kOhm [CR0603-FX-3011ELF]
3 Ohm [CR2010-J/-3R0ELF]	3 Ohm [PWR163S-25-3R00J]	3 Ohm [PWR4318W3R00JE]	3.01 kOhm [CR0805-FX-3011ELF]
3 Ohm [CR2512-J/-3R0ELF]	3 Ohm [PWR220T-20-3R00F]	3 uH [SRN6028-3R0Y]	3.01 kOhm [CR1206-FX-3011ELF]
3 Ohm [CRL0603-FW-3R00ELF]	3 Ohm [PWR220T-20-3R00J]	3 uH [SRR1003-3R0M]	3.01 kOhm [CRM1206-FX-3011ELF]
3 Ohm [CRL0603-JW-3R00ELF]	3 Ohm [PWR220T-35-3R00F]	3 uH [SRR1005-3R0M]	
3 Ohm [CRL0805-FW-3R00ELF]	3 Ohm [PWR221T-30-3R00F]	3 uH [SRR5018-3R0Y]	

Multisim 14.1 Base Edition Components

3.01 kOhm [CRT0402-FZ- 3011GLF]	3.16 kOhm [CR0402-FX- 3161GLF]	3.24 kOhm [CR0805-FX- 3241ELF]	3.3 kOhm [4306H- 101-332]
3.01 kOhm [CRT0603-FZ- 3011ELF]	3.16 kOhm [CR0603-FX- 3161ELF]	3.24 kOhm [CR1206-FX- 3241ELF]	3.3 kOhm [4306H- 101-332LF]
3.01 kOhm [CRT0805-BY- 3011ELF]	3.16 kOhm [CR0805-FX- 3161ELF]	3.24 kOhm [CR2010-FX- 3241ELF]	3.3 kOhm [4306H- 102-332]
3.01 kOhm [CRT0805-FZ- 3011ELF]	3.16 kOhm [CR1206-FX- 3161ELF]	3.24 kOhm [CRT0805-BY- 3241ELF]	3.3 kOhm [4306M- 102-332]
3.01 Ohm [CRM1206-FX- 3R01ELF]	3.16 kOhm [CRT0402-FZ- 3161GLF]	3.3 kOhm [4108R- 1-332]	3.3 kOhm [4306M- 102-332LF]
3.01 Ohm [CRM2010-FX- 3R01ELF]	3.16 kOhm [CRT0603-FX- 3161ELF]	3.3 kOhm [4108R- 1-332LF]	3.3 kOhm [4306R- 101-332]
3.09 kOhm [CR0402-FX- 3091GLF]	3.16 kOhm [CRT0603-FZ- 3161ELF]	3.3 kOhm [4114R- 1-332]	3.3 kOhm [4306R- 101-332LF]
3.09 kOhm [CR0603-FX- 3091ELF]	3.16 kOhm [CRT1206-BY- 3161ELF]	3.3 kOhm [4114R- 1-332LF]	3.3 kOhm [4306R- 102-332]
3.09 kOhm [CR0805-FX- 3091ELF]	3.2 kOhm [4310R- 101-322]	3.3 kOhm [4114R- 2-332]	3.3 kOhm [4306R- 102-332LF]
3.09 kOhm [CR1206-FX- 3091ELF]	3.2 uH [SRP1045- 3R2M]	3.3 kOhm [4114R- 2-332LF]	3.3 kOhm [4308H- 101-332]
3.09 MOhm [CR0603-FX- 3094ELF]	3.24 kOhm [CR0402-FX- 3241GLF]	3.3 kOhm [4116R- 1-332]	3.3 kOhm [4308H- 102-332]
	3.24 kOhm [CR0603-FX- 3241ELF]	3.3 kOhm [4116R- 1-332LF]	3.3 kOhm [4308H- 102-332LF]
		3.3 kOhm [4116R- 2-332]	3.3 kOhm [4308M- 101-332]
		3.3 kOhm [4116R- 2-332LF]	3.3 kOhm [4308R- 101-332]

Multisim 14.1 Base Edition Components

3.3 kOhm [4308R-101-332LF]	3.3 kOhm [4416P-T02-332]	3.3 kOhm [4607X-101-332LF]	3.3 kOhm [4610X-AP1-332LF]
3.3 kOhm [4308R-102-332]	3.3 kOhm [4420P-1-332]	3.3 kOhm [4608H-101-332LF]	3.3 kOhm [4611X-101-332LF]
3.3 kOhm [4308R-102-332LF]	3.3 kOhm [4420P-2-332]	3.3 kOhm [4608H-102-332LF]	3.3 kOhm [4612X-102-332LF]
3.3 kOhm [4309R-101-332]	3.3 kOhm [4420P-2-332LF]	3.3 kOhm [4608M-102-332LF]	3.3 kOhm [4814P-1-332]
3.3 kOhm [4309R-101-332LF]	3.3 kOhm [4420P-T02-332]	3.3 kOhm [4608X-101-332LF]	3.3 kOhm [4814P-1-332LF]
3.3 kOhm [4310H-101-332]	3.3 kOhm [4604X-101-332LF]	3.3 kOhm [4608X-102-332LF]	3.3 kOhm [4814P-2-332]
3.3 kOhm [4310H-101-332LF]	3.3 kOhm [4604X-102-332LF]	3.3 kOhm [4608X-AP1-332LF]	3.3 kOhm [4814P-2-332LF]
3.3 kOhm [4310H-102-332]	3.3 kOhm [4605M-101-332LF]	3.3 kOhm [4608X-AP2-332LF]	3.3 kOhm [4814P-T01-332]
3.3 kOhm [4310M-101-332]	3.3 kOhm [4605X-101-332LF]	3.3 kOhm [4609H-101-332LF]	3.3 kOhm [4814P-T01-332LF]
3.3 kOhm [4310M-101-332LF]	3.3 kOhm [4605X-AP1-332LF]	3.3 kOhm [4609X-101-332LF]	3.3 kOhm [4814P-T02-332]
3.3 kOhm [4310R-101-332]	3.3 kOhm [4606H-101-332LF]	3.3 kOhm [4609X-AP1-332LF]	3.3 kOhm [4814P-T02-332LF]
3.3 kOhm [4310R-101-332LF]	3.3 kOhm [4606X-101-332LF]	3.3 kOhm [4610H-101-332LF]	3.3 kOhm [4816P-1-332]
3.3 kOhm [4310R-102-332]	3.3 kOhm [4606X-102-332LF]	3.3 kOhm [4610M-101-332LF]	3.3 kOhm [4816P-1-332LF]
3.3 kOhm [4310R-102-332LF]	3.3 kOhm [4606X-AP1-332LF]	3.3 kOhm [4610X-101-332LF]	3.3 kOhm [4816P-2-332]
3.3 kOhm [4416P-2-332]	3.3 kOhm [4607M-101-332LF]	3.3 kOhm [4610X-102-332LF]	3.3 kOhm [4816P-2-332LF]

Multisim 14.1 Base Edition Components

3.3 kOhm [4816P-T01-332]	3.3 kOhm [CAT16-332J8LF]	3.3 kOhm [CR0805-FX-3301GLF]	3.3 kOhm [CRT0805-DY-3301ELF]
3.3 kOhm [4816P-T01-332LF]	3.3 kOhm [CAT25-332JALF]	3.3 kOhm [CR0805-JW-332ELF]	3.3 kOhm [CRT0805-PV-3301ELF]
3.3 kOhm [4816P-T02-332]	3.3 kOhm [CAY10-332J4LF]	3.3 kOhm [CR1206-FX-3301ELF]	3.3 kOhm [PWR163S-25-3301J]
3.3 kOhm [4816P-T02-332LF]	3.3 kOhm [CAY16-3301F4LF]	3.3 kOhm [CR1206-JW-332ELF]	3.3 kOhm [PWR220T-20-3301F]
3.3 kOhm [4818P-2-332]	3.3 kOhm [CAY16-332J4LF]	3.3 kOhm [CR1206-JW-332GLF]	3.3 kOhm [PWR220T-20-3301F]
3.3 kOhm [4818P-2-332LF]	3.3 kOhm [CAY16-332J8LF]	3.3 kOhm [CR2010-JW-332ELF]	3.3 kOhm [PWR220T-20-3301J]
3.3 kOhm [4818P-T02-332]	3.3 kOhm [CAY17-332JALF]	3.3 kOhm [CR2512-FX-3301ELF]	3.3 kOhm [PWR221T-30-3301F]
3.3 kOhm [4820P-2-332]	3.3 kOhm [CR0201-JW-332GLF]	3.3 kOhm [CR2512-JW-332ELF]	3.3 kOhm [PWR263S-20-3301F]
3.3 kOhm [4820P-2-332F]	3.3 kOhm [CR0402-FX-3301GLF]	3.3 kOhm [CRM1206-FX-3301ELF]	3.3 kOhm [PWR263S-20-3301F]
3.3 kOhm [4820P-T02-332]	3.3 kOhm [CR0402-JW-332GLF]	3.3 kOhm [CRM1206-JW-332ELF]	3.3 kOhm [PWR263S-20-3301J]
3.3 kOhm [4820P-T02-332LF]	3.3 kOhm [CR0603-FX-3301ELF]	3.3 kOhm [CRT0603-BY-3301ELF]	3.3 kOhm [PWR263S-35-3301F]
3.3 kOhm [CAT10-332J4LF]	3.3 kOhm [CR0603-FX-3301HLF]	3.3 kOhm [CRT0603-DY-3301ELF]	3.3 kOhm [PWR263S-35-3301J]
3.3 kOhm [CAT16-3301F4LF]	3.3 kOhm [CR0603-JW-332ELF]	3.3 kOhm [CRT0603-PW-3301ELF]	
3.3 kOhm [CAT16-3301F8LF]	3.3 kOhm [CR0603-JW-332GLF]		
3.3 kOhm [CAT16-332J4LF]	3.3 kOhm [CR0805-FX-3301ELF]		

Multisim 14.1 Base Edition Components

3.3 kOhm [WS5M3301J]	3.3 MOhm [CAT25- 335JALF]	3.3 nF [C0402C332K8RACT U]	3.3 nF [C0805C332K1HACT U]
3.3 mH [SDR0503- 332JL]	3.3 MOhm [CHV0603-FX- 3304ELF]	3.3 nF [C0402C332K9RACT U]	3.3 nF [C0805C332K1RACT U]
3.3 mH [SDR0805- 332KL]	3.3 MOhm [CHV0805-JW- 335ELF]	3.3 nF [C0603C332K1HACT U]	3.3 nF [C0805C332K2RACT U]
3.3 mH [SDR1005- 332KL]	3.3 MOhm [CHV1206-FX- 3304ELF]	3.3 nF [C0603C332K1RACT U]	3.3 nF [C0805C332K3GACT U]
3.3 mH [SDR1006- 332KL]	3.3 MOhm [CHV2010-FX- 3304ELF]	3.3 nF [C0603C332K3GACT U]	3.3 nF [C0805C332K3HACT U]
3.3 mH [SRE6603- 332M]	3.3 MOhm [CR0603-JW- 335ELF]	3.3 nF [C0603C332K3HACT U]	3.3 nF [C0805C332K4GACT U]
3.3 mH [SRR0906- 332YL]	3.3 MOhm [CR0805-JW- 335ELF]	3.3 nF [C0603C332K3RACT U]	3.3 nF [C0805C332K4RACT U]
3.3 mH [SRR1005- 332K]	3.3 MOhm [CR1206-JW- 335ELF]	3.3 nF [C0603C332K4RACT U]	3.3 nF [C0805C332K5GACT U]
3.3 mH [SRR1208- 332KL]	3.3 nF [C0402C332K3RACT U]	3.3 nF [C0603C332K5HACT U]	3.3 nF [C0805C332K5HACT U]
3.3 mH [SRR6603- 332ML]	3.3 nF [C0402C332K4RACT U]	3.3 nF [C0603C332K5RACT U]	3.3 nF [C0805C332K5RACT U]
3.3 MOhm [4608X- 102-335LF]	3.3 nF [C0402C332K5RACT U]	3.3 nF [C0805C332K1GACT U]	3.3 nF [C0805C332K8GACT U]
3.3 MOhm [4609X- 101-335LF]			
3.3 MOhm [4610X- 101-335LF]			

Multisim 14.1 Base Edition Components

3.3 nF [C0805C332KARACT U]	3.3 nF [C1825C332KBGAC TU]	3.3 nF [GMC7.3333K250K3 5TR12]	3.3 nF [MMC7.3332K50K3 1TR12]
3.3 nF [C1206C332K1GACT U]	3.3 nF [C2220C332KBGAC TU]	3.3 nF [GPC7.3332K160K3 1TR12]	3.3 nF [MMC7.3332K63K3 1TR12]
3.3 nF [C1206C332K1RACT U]	3.3 nF [C2225C332KBGAC TU]	3.3 nF [GPC7.3332K400K3 1TR12]	3.3 nF [SPC7.3332K100K31 TR12]
3.3 nF [C1206C332K2RACT U]	3.3 nF [CA064C332K1RACT U]	3.3 nF [GPC7.3332K630K3 3TR12]	3.3 nF [SPC7.3332K250K31 TR12]
3.3 nF [C1206C332K3RACT U]	3.3 nF [CA064C332K5RACT U]	3.3 nF [GPC7.3332K63K31 TR12]	3.3 nF [SPC7.3332K400K33 TR12]
3.3 nF [C1206C332K5GACT U]	3.3 nF [GMC5.7332K100J3 1TR12]	3.3 nF [MMC5.7332K100J 31TR12]	3.3 nF [SPC7.3332K630K35 TR12]
3.3 nF [C1206C332K5RACT U]	3.3 nF [GMC5.7332K50J31 TR12]	3.3 nF [MMC5.7332K250J 31TR12]	3.3 Ohm [CR0402- J/-3R3GLF]
3.3 nF [C1210C332K1RACT U]	3.3 nF [GMC5.7333K100J3 3TR12]	3.3 nF [MMC5.7332K50J3 1TR12]	3.3 Ohm [CR0603- J/-3R3ELF]
3.3 nF [C1210C332K2GACT U]	3.3 nF [GMC7.3332K100K3 1TR12]	3.3 nF [MMC7.3332K100K 31TR12]	3.3 Ohm [CR1206- J/-3R3ELF]
3.3 nF [C1210C332K5GACT U]	3.3 nF [GMC7.3332K400K3 1TR12]	3.3 nF [MMC7.3332K250K 31TR12]	3.3 Ohm [CR2010- J/-3R3ELF]
3.3 nF [C1210C332K5RACT U]	3.3 nF [GMC7.3333K100K3 1TR12]	3.3 nF [MMC7.3332K400K 31TR12]	3.3 Ohm [CR2512- J/-3R3ELF]
			3.3 Ohm [CRL0603- FW-3R30ELF]

Multisim 14.1 Base Edition Components

3.3 Ohm [CRL0603-JW-3R30ELF]	3.3 Ohm [PWR163S-25-3R30J]	3.3 Ohm [PWR263S-20-3R30JE]	3.3 uF [C1206C335K8RACTU]
3.3 Ohm [CRL0805-FW-3R30ELF]	3.3 Ohm [PWR220T-20-3R30F]	3.3 Ohm [PWR263S-35-3R30F]	3.3 uF [C1206C335K9PACTU]
3.3 Ohm [CRL0805-JW-3R30ELF]	3.3 Ohm [PWR220T-20-3R30J]	3.3 Ohm [PWR263S-35-3R30J]	3.3 uF [C1206C335K9RACTU]
3.3 Ohm [CRL1206-JW-3R30ELF]	3.3 Ohm [PWR220T-35-3R30F]	3.3 uF [06126D335KAT2A]	3.3 uF [C1206C335M4VAC TU]
3.3 Ohm [CRL2010-FW-3R30ELF]	3.3 Ohm [PWR220T-35-3R30J]	3.3 uF [C0805C335K4PACTU]	3.3 uF [C1206C335M9VAC TU]
3.3 Ohm [CRL2010-JW-3R30ELF]	3.3 Ohm [PWR221T-30-3R30F]	3.3 uF [C0805C335K8PACTU]	3.3 uF [C1210C335K3PACTU]
3.3 Ohm [CRM2010-JW-3R3ELF]	3.3 Ohm [PWR221T-30-3R30J]	3.3 uF [C0805C335K9PACTU]	3.3 uF [C1210C335K4PACTU]
3.3 Ohm [CRM2512-JW-3R3ELF]	3.3 Ohm [PWR2615W3R30F]	3.3 uF [C1206C335K3PACTU]	3.3 uF [C1210C335K4RACTU]
3.3 Ohm [CRS0805-JW-3R3ELF]	3.3 Ohm [PWR2615W3R30F E]	3.3 uF [C1206C335K4PACTU]	3.3 uF [C1210C335K8PACTU]
3.3 Ohm [CRS1206-FW-3R30ELF]	3.3 Ohm [PWR2615W3R30J]	3.3 uF [C1206C335K4RACTU]	3.3 uF [MDC10335K100A5 2P3TUBE]
3.3 Ohm [CRS2512-FW-3R30ELF]	3.3 Ohm [PWR263S-20-3R30F]	3.3 uF [C1206C335K8PACTU]	3.3 uF [MDC10335K50A52 P3TUBE]
3.3 Ohm [PWR163S-25-3R30F]	3.3 Ohm [PWR263S-20-3R30J]		

Multisim 14.1 Base Edition Components

3.3 uF [MDC15335K100B5 3P3TUBE]	3.3 uF [T491B335M025AT]	3.3 uF [T494B335M016AT]	3.3 uF [T495C335M035AT E600]
3.3 uF [MDC15335K50B53 P3TUBE]	3.3 uF [T491B335M035AT]	3.3 uF [T494B335M020AT]	3.3 uF [T498A335M010AT E3K6]
3.3 uF [MDK10335K50A52 P3TUBE]	3.3 uF [T491C335M025AT]	3.3 uF [T494B335M025AT]	3.3 uF [T498A335M016AT E3K4]
3.3 uF [MDS10335K50A52 P3TUBE]	3.3 uF [T491D335M035AT]	3.3 uF [T494C335M025AT]	3.3 uF [T498C335M035AT E1K7]
3.3 uF [T409B335M006AH 4250]	3.3 uF [T491D335M050AT]	3.3 uF [T494C335M035AT]	3.3 uF [TACL335K002RTA]
3.3 uF [T489A335M020AT E3K7]	3.3 uF [T491S335M010AT]	3.3 uF [T494D335M050AT]	3.3 uF [TACL335K003RTA]
3.3 uF [T491A335M004AT]	3.3 uF [T491T335M020AT]	3.3 uF [T494S335M010AT]	3.3 uF [TACL335K006RTA]
3.3 uF [T491A335M006AT]	3.3 uF [T493A335M004AH 6110]	3.3 uF [T494T335M020AT]	3.3 uF [TACR335K010RTA]
3.3 uF [T491A335M010AT]	3.3 uF [T493A335M004AH 6110]	3.3 uF [T495A335M016AT E3K0]	3.3 uF [TAJA335K006RNJ]
3.3 uF [T491A335M016AT]	3.3 uF [T494A335M004AT]	3.3 uF [T495B335M035AT E900]	3.3 uF [TAJA335K010RNJ]
3.3 uF [T491A335M020AT]	3.3 uF [T494A335M006AT]	3.3 uF [T495B335M035AT E900]	3.3 uF [TAJA335K016RNJ]
3.3 uF [T491A335M020AT]	3.3 uF [T494A335M010AT]	3.3 uF [T495C335M035AT E525]	3.3 uF [TAJA335K020RNJ]
3.3 uF [T491B335M016AT]	3.3 uF [T494A335M016AT]	3.3 uF [T495C335M035AT E525]	3.3 uF [TAJA335K025RNJ]
3.3 uF [T491B335M020AT]	3.3 uF [T494A335M020AT]	3.3 uF [T495C335M035AT E550]	3.3 uF [TAJA335K025RNJ]
			3.3 uF [TAJB335K016RNJ]

Multisim 14.1 Base Edition Components

3.3 uF [TAJB335K020RNJ]	3.3 uF [TAJT335K010RNJ]	3.3 uF [TPSB335K025R200 0]	3.3 uH [SDR0604- 3R3ML]
3.3 uF [TAJB335K025RNJ]	3.3 uF [TAJT335K016RNJ]	3.3 uF [TPSC335K035R070 0]	3.3 uH [SDR0703- 3R3ML]
3.3 uF [TAJB335K035RNJ]	3.3 uF [TAJT335K020RNJ]		3.3 uH [SDR0805- 3R3ML]
3.3 uF [TAJC335K025RNJ]	3.3 uF [TAJT335K025RNJ]	3.3 uF [TPSC335K050R100 0]	3.3 uH [SDR1005- 3R3ML]
3.3 uF [TAJC335K035RNJ]	3.3 uF [TAJY335K050RNJ]	3.3 uF [TPSD335K050R080 0]	3.3 uH [SDR1006- 3R3ML]
3.3 uF [TAJC335K050RNJ]	3.3 uF [THJA335K010RJN]	3.3 uF [TPST335K010R150 0]	3.3 uH [SDR1307- 3R3ML]
3.3 uF [TAJD335K050RNJ]	3.3 uF [THJA335K016RJN]		3.3 uH [SDR1307A- 3R3M]
3.3 uF [TAJR335K004RNJ]	3.3 uF [THJB335K020RJN]	3.3 uF [TRJB335K035RRJ]	3.3 uH [SDR1806- 3R3ML]
3.3 uF [TAJR335K006RNJ]	3.3 uF [THJC335K035RJN]	3.3 uH [SDE0403A- 3R3M]	3.3 uH [SDR6603- 3R3M]
3.3 uF [TAJR335K010RNJ]	3.3 uF [TPSA335K016R350 0]	3.3 uH [SDE0604A- 3R3M]	3.3 uH [SDR7045- 3R3M]
3.3 uF [TAJR335K016RNJ]	3.3 uF [TPSA335K020R250 0]	3.3 uH [SDE0805A- 3R3M]	3.3 uH [SRN3010- 3R3M]
3.3 uF [TAJS335K004RNJ]		3.3 uH [SDE1006A- 3R3M]	3.3 uH [SRN3015- 3R3M]
3.3 uF [TAJS335K006RNJ]	3.3 uF [TPSB335K016R250 0]	3.3 uH [SDR0302- 3R3ML]	3.3 uH [SRN4012T- 3R3M]
3.3 uF [TAJS335K010RNJ]	3.3 uF [TPSB335K020R130 0]	3.3 uH [SDR0403- 3R3ML]	3.3 uH [SRN4018- 3R3M]
3.3 uF [TAJS335K016RNJ]		3.3 uH [SDR0603- 3R3ML]	3.3 uH [SRN4026- 3R3M]

Multisim 14.1 Base Edition Components

3.3 uH [SRN5020-3R3M]	3.3 uH [SRP5015TA-3R3M]	3.3 uH [SRR1240-3R3Y]	3.3 uH [SRU2009-3R3Y]
3.3 uH [SRN5040-3R3M]	3.3 uH [SRP5030T-3R3M]	3.3 uH [SRR1260-3R3Y]	3.3 uH [SRU2011-3R3Y]
3.3 uH [SRN6028-3R3M]	3.3 uH [SRP5030TA-3R3M]	3.3 uH [SRR1260A-3R3Y]	3.3 uH [SRU2013-3R3Y]
3.3 uH [SRN6045-3R3Y]	3.3 uH [SRP6540-3R3M]	3.3 uH [SRR1280-3R3Y]	3.3 uH [SRU3011-3R3Y]
3.3 uH [SRN8040-3R3Y]	3.3 uH [SRP7028A-3R3M]	3.3 uH [SRR3011-3R3YL]	3.3 uH [SRU3017-3R3Y]
3.3 uH [SRP1038A-3R3M]	3.3 uH [SRP7030-3R3FM]	3.3 uH [SRR4011-3R3YL]	3.3 uH [SRU5011-3R3Y]
3.3 uH [SRP1040-3R3M]	3.3 uH [SRP7050TA-3R3M]	3.3 uH [SRR4018-3R3Y]	3.3 uH [SRU5016-3R3Y]
3.3 uH [SRP1235-3R3M]	3.3 uH [SRR0603-3R3ML]	3.3 uH [SRR4028-3R3Y]	3.3 uH [SRU5028-3R3Y]
3.3 uH [SRP1250-3R3M]	3.3 uH [SRR0604-3R3ML]	3.3 uH [SRR6028-3R3Y]	3.3 uH [SRU5028A-3R3Y]
3.3 uH [SRP1265A-3R3M]	3.3 uH [SRR0618-3R3ML]	3.3 uH [SRR6038-3R3Y]	3.3 uH [SRU6018-3R3Y]
3.3 uH [SRP1270-3R3M]	3.3 uH [SRR1005-3R3M]	3.3 uH [SRR6603-3R3ML]	3.3 uH [SRU6025-3R3Y]
3.3 uH [SRP1770TA-3R3M]	3.3 uH [SRR1205-3R3ML]	3.3 uH [SRR7032-3R3M]	3.3 uH [SRU6025A-3R3Y]
3.3 uH [SRP4012TA-3R3M]	3.3 uH [SRR1206-3R3ML]	3.3 uH [SRR7045-3R3M]	3.3 uH [SRU8028-3R3Y]
3.3 uH [SRP4020-3R3M]	3.3 uH [SRR1210-3R3Y]	3.3 uH [SRU1028-3R3Y]	3.3 uH [SRU8028A-3R3Y]
3.3 uH [SRP4020TA-3R3M]	3.3 uH [SRR1210A-3R3Y]	3.3 uH [SRU1028A-3R3Y]	3.32 kOhm [CAY16-3321F4LF]

Multisim 14.1 Base Edition Components

3.32 kOhm [CR0402-FX- 3321GLF]	3.4 kOhm [CR0805- FX-3401ELF]	3.5 uH [SRP1206- 3R3Z]	3.6 kOhm [4116R- 1-362]
3.32 kOhm [CR0603-FX- 3321ELF]	3.4 kOhm [CR1206- FX-3401ELF]	3.5 uH [SRR0906- 3R5ML]	3.6 kOhm [4308M- 102-362]
3.32 kOhm [CR0805-FX- 3321ELF]	3.4 kOhm [CRT0603-BY- 3401ELF]	3.5 uH [SRR1260- 3R5Y]	3.6 kOhm [4308M- 102-362LF]
3.32 kOhm [CR1206-FX- 3321ELF]	3.4 kOhm [CRT0805-BY- 3401ELF]	3.5 uH [SRR1260A- 3R5Y]	3.6 kOhm [4609X- 101-362LF]
3.32 kOhm [CR1206-FX- 3321ELF]	3.48 kOhm [CR0402-FX- 3481GLF]	3.5 uH [SRR1280- 3R5Y]	3.6 kOhm [CAY10- 362J4LF]
3.32 kOhm [CRT0402-FZ- 3321GLF]	3.48 kOhm [CR0603-FX- 3481ELF]	3.5 uH [SRU1038- 3R5Y]	3.6 kOhm [CAY16- 3601F4LF]
3.32 kOhm [CRT0603-BY- 3321ELF]	3.48 kOhm [CR0805-FX- 3481ELF]	3.5 uH [SRU1038A- 3R5Y]	3.6 kOhm [CAY16- 362J4LF]
3.32 kOhm [CRT0805-BY- 3321ELF]	3.48 kOhm [CR1206-FX- 3481ELF]	3.5 uH [SRU5018- 3R5Y]	3.6 kOhm [CR0201- FW-3601GLF]
3.32 kOhm [CRT1206-FZ- 3321ELF]	3.48 kOhm [CRT1206-BY- 3481ELF]	3.57 kOhm [CR0402-FX- 3571GLF]	3.6 kOhm [CR0402- FX-3601GLF]
3.32 MOhm [CR1206-FW- 3324ELF]	3.5 Ohm [PWR6327W3R50J]	3.57 kOhm [CR0603-FX- 3571ELF]	3.6 kOhm [CR0402- JW-362GLF]
3.32 Ohm [CRM1206-FX- 3R32ELF]	3.5 uH [SDR1305- 3R5Y]	3.57 kOhm [CR0805-FX- 3571ELF]	3.6 kOhm [CR0603- FX-3601ELF]
3.4 kOhm [CR0402- FX-3401GLF]	3.5 uH [SDR7030- 3R5M]	3.57 kOhm [CR1206-FX- 3571ELF]	3.6 kOhm [CR0805- JW-362ELF]
3.4 kOhm [CR0603- FX-3401ELF]	3.5 uH [SRP1205- 3R3Y]	3.6 kOhm [4114R- 1-362]	3.6 kOhm [CR1206- FX-3601ELF]
		3.6 kOhm [4114R- 1-362LF]	

Multisim 14.1 Base Edition Components

3.6 kOhm [CR1206-FX-3601GLF]	3.6 nF [C0805C362K1HACT U]	3.6 Ohm [CRL1206-FW-3R60ELF]	3.65 kOhm [CRT0603-BY-3651ELF]
3.6 kOhm [CR1206-JW-362ELF]	3.6 nF [C0805C362K3HACT U]	3.6 Ohm [CRL1206-JW-3R60ELF]	3.65 kOhm [CRT0603-DY-3651ELF]
3.6 kOhm [CR2512-JW-362ELF]	3.6 nF [C0805C362K5HACT U]	3.6 Ohm [CRL2010-FW-3R60ELF]	3.65 kOhm [CRT0805-FY-3651ELF]
3.6 kOhm [CRM1206-JW-362ELF]	3.6 nF [C1825C362KBGAC TU]	3.6 Ohm [CRL2010-JW-3R60ELF]	3.74 kOhm [CR0402-FX-3741GLF]
3.6 MOhm [CR0603-JW-365ELF]	3.6 nF [C2220C362KBGAC TU]	3.6 Ohm [CRM0805-JW-3R6ELF]	3.74 kOhm [CR0603-FX-3741ELF]
3.6 MOhm [CR0805-FW-3604ELF]	3.6 nF [C2225C362KBGAC TU]	3.6 Ohm [CRM2512-JW-3R6ELF]	3.74 kOhm [CR0805-FX-3741ELF]
3.6 MOhm [CR1206-JW-365ELF]	3.6 Ohm [CR0603-J/-3R6ELF]	3.6 uH [SRN8040-3R6Y]	3.74 kOhm [CR1206-FX-3741ELF]
3.6 nF [C0603C362K1HACT U]	3.6 Ohm [CR0805-J/-3R6ELF]	3.65 kOhm [CR0402-FX-3651GLF]	3.74 kOhm [CR1206-FX-3741GLF]
3.6 nF [C0603C362K3HACT U]	3.6 Ohm [CR1206-J/-3R6ELF]	3.65 kOhm [CR0603-FX-3651ELF]	3.74 kOhm [CRT0603-BW-3741ELF]
3.6 nF [C0603C362K5HACT U]	3.6 Ohm [CRL0603-FW-3R60ELF]	3.65 kOhm [CR0805-FX-3651ELF]	3.74 kOhm [CRT0805-DX-3741ELF]
3.6 nF [C0805C362K1GACT U]	3.6 Ohm [CRL0805-FW-3R60ELF]	3.65 kOhm [CR1206-FX-3651ELF]	3.8 kOhm [4308R-102-382]
	3.6 Ohm [CRL0805-JW-3R60ELF]	3.65 kOhm [CR2010-FX-3651ELF]	3.8 uH [SRU1038-3R8Y]

Multisim 14.1 Base Edition Components

3.83 kOhm [CR0402-FX- 3831GLF]	3.9 kOhm [4116R- 2-392LF]	3.9 kOhm [4308R- 102-392]	3.9 kOhm [4604X- 102-392LF]
3.83 kOhm [CR0603-FX- 3831ELF]	3.9 kOhm [4306M- 101-392]	3.9 kOhm [4308R- 102-392LF]	3.9 kOhm [4605X- 101-392LF]
3.83 kOhm [CR0805-FX- 3831ELF]	3.9 kOhm [4306M- 101-392LF]	3.9 kOhm [4309R- 101-392]	3.9 kOhm [4606H- 102-392LF]
3.83 kOhm [CR1206-FX- 3831ELF]	3.9 kOhm [4306R- 101-392]	3.9 kOhm [4309R- 101-392LF]	3.9 kOhm [4606X- 101-392LF]
3.83 kOhm [CR1206-FX- 3831ELF]	3.9 kOhm [4306R- 101-392LF]	3.9 kOhm [4310M- 101-392]	3.9 kOhm [4606X- 102-392LF]
3.83 kOhm [CRT0402-FZ- 3831GLF]	3.9 kOhm [4306R- 102-392]	3.9 kOhm [4310M- 101-392LF]	3.9 kOhm [4606X- AP1-392LF]
3.83 MOhm [CR0805-FX- 3834ELF]	3.9 kOhm [4306R- 102-392LF]	3.9 kOhm [4310M- 102-392]	3.9 kOhm [4606X- AP2-392LF]
3.9 kOhm [4114R- 1-392]	3.9 kOhm [4308H- 101-392]	3.9 kOhm [4310R- 101-392]	3.9 kOhm [4607X- 101-392LF]
3.9 kOhm [4114R- 1-392LF]	3.9 kOhm [4308H- 102-392]	3.9 kOhm [4310R- 101-392LF]	3.9 kOhm [4608H- 102-392LF]
3.9 kOhm [4114R- 2-392]	3.9 kOhm [4308M- 101-392]	3.9 kOhm [4310R- 102-392]	3.9 kOhm [4608X- 101-392LF]
3.9 kOhm [4114R- 2-392LF]	3.9 kOhm [4308M- 101-392LF]	3.9 kOhm [4310R- 102-392LF]	3.9 kOhm [4608X- 102-392LF]
3.9 kOhm [4116R- 1-392]	3.9 kOhm [4308M- 102-392]	3.9 kOhm [4420P- 2-392]	3.9 kOhm [4609H- 101-392LF]
3.9 kOhm [4116R- 1-392LF]	3.9 kOhm [4308M- 102-392LF]	3.9 kOhm [4420P- T01-392]	3.9 kOhm [4609X- 101-392LF]
3.9 kOhm [4116R- 2-392]	3.9 kOhm [4308R- 101-392]	3.9 kOhm [4420P- T02-392]	3.9 kOhm [4610H- 101-392LF]
	3.9 kOhm [4308R- 101-392LF]	3.9 kOhm [4604X- 101-392LF]	3.9 kOhm [4610H- 102-392LF]

Multisim 14.1 Base Edition Components

3.9 kOhm [4610X-101-392LF]	3.9 kOhm [CAT16-392J8LF]	3.9 kOhm [CR2010-JW-392ELF]	3.9 MOhm [CR0603-JW-395ELF]
3.9 kOhm [4610X-102-392LF]	3.9 kOhm [CAT25-392JALF]	3.9 kOhm [CR2512-JW-392ELF]	3.9 MOhm [CR0805-JW-395ELF]
3.9 kOhm [4612X-102-392LF]	3.9 kOhm [CAY10-392J4LF]	3.9 kOhm [CRM1206-JW-392ELF]	3.9 MOhm [CR1206-JW-395ELF]
3.9 kOhm [4816P-1-392]	3.9 kOhm [CAY16-3901F4LF]	3.9 kOhm [CRT1206-AV-3901ELF]	3.9 nF [C0402C392K3RACT U]
3.9 kOhm [4816P-1-392LF]	3.9 kOhm [CAY16-392J4LF]	3.9 mH [SDR0503-392JL]	3.9 nF [C0402C392K4RACT U]
3.9 kOhm [4816P-2-392]	3.9 kOhm [CAY16-392J8LF]	3.9 mH [SDR0805-392KL]	3.9 nF [C0402C392K5RACT U]
3.9 kOhm [4816P-2-392LF]	3.9 kOhm [CR0402-FX-3901GLF]	3.9 mH [SDR0906-392KL]	3.9 nF [C0603C392K1HACT U]
3.9 kOhm [4816P-T01-392]	3.9 kOhm [CR0402-JW-392GLF]	3.9 mH [SDR1006-392KL]	3.9 nF [C0603C392K1RACT U]
3.9 kOhm [4816P-T01-392LF]	3.9 kOhm [CR0603-FX-3901ELF]	3.9 mH [SRR0906-392YL]	3.9 nF [C0603C392K3GACT U]
3.9 kOhm [4816P-T02-392]	3.9 kOhm [CR0603-JW-392ELF]	3.9 mH [SRR1208-392KL]	3.9 nF [C0603C392K3HACT U]
3.9 kOhm [4816P-T02-392LF]	3.9 kOhm [CR0603-JW-392GLF]	3.9 MOhm [CAT25-395JALF]	3.9 nF [C0603C392K3RACT U]
3.9 kOhm [4820P-2-392]	3.9 kOhm [CR0805-FX-3901ELF]	3.9 MOhm [CHV0805-FX-3904ELF]	
3.9 kOhm [4820P-T02-392]	3.9 kOhm [CR0805-JW-392ELF]	3.9 MOhm [CR0603-FX-3904ELF]	
3.9 kOhm [CAT16-3901F4LF]	3.9 kOhm [CR1206-FX-3901ELF]		
3.9 kOhm [CAT16-392J4LF]	3.9 kOhm [CR1206-JW-392ELF]		

Multisim 14.1 Base Edition Components

3.9 nF [C0603C392K4RACT U]	3.9 nF [C0805C392K4RACT U]	3.9 nF [C1812C392K2GACT U]	3.9 nF [GMC7.3393K100K3 1TR12]
3.9 nF [C0603C392K5HACT U]	3.9 nF [C0805C392K5GACT U]	3.9 nF [C1825C392KBGAC TU]	3.9 nF [GMC7.3393K250K3 7TR12]
3.9 nF [C0603C392K5RACT U]	3.9 nF [C0805C392K5HACT U]	3.9 nF [C2220C392KBGAC TU]	3.9 nF [MMC5.7392K100J 31TR12]
3.9 nF [C0805C392K1GACT U]	3.9 nF [C0805C392K5RACT U]	3.9 nF [C2225C392KBGAC TU]	3.9 nF [MMC5.7392K250J 31TR12]
3.9 nF [C0805C392K1HACT U]	3.9 nF [C0805C392KARACT U]	3.9 nF [C2225C392KCGAC TU]	3.9 nF [MMC5.7392K50J3 1TR12]
3.9 nF [C0805C392K1RACT U]	3.9 nF [C1206C392K1GACT U]	3.9 nF [CDR02BX392BKSM]	3.9 nF [MMC7.3392K100K 31TR12]
3.9 nF [C0805C392K2RACT U]	3.9 nF [C1206C392K1RACT U]	3.9 nF [GMC5.7392K100J3 1TR12]	3.9 nF [MMC7.3392K250K 31TR12]
3.9 nF [C0805C392K3GACT U]	3.9 nF [C1206C392K2RACT U]	3.9 nF [GMC5.7392K50J31 TR12]	3.9 nF [MMC7.3392K400K 31TR12]
3.9 nF [C0805C392K3HACT U]	3.9 nF [C1206C392K5GACT U]	3.9 nF [GMC5.7393K100J3 5TR12]	3.9 nF [MMC7.3392K50K3 1TR12]
3.9 nF [C0805C392K3RACT U]	3.9 nF [C1206C392K5RACT U]	3.9 nF [GMC7.3392K100K3 1TR12]	3.9 nF [MMC7.3392K63K3 1TR12]
3.9 nF [C0805C392K4GACT U]	3.9 nF [C1210C392K5RACT U]	3.9 nF [GMC7.3392K400K3 1TR12]	3.9 Ohm [CR0402- J/-3R9GLF] 3.9 Ohm [CR0603- J/-3R9ELF]

Multisim 14.1 Base Edition Components

3.9 Ohm [CR0603-J/-3R9GLF]	3.9 Ohm [PWR263S-35-3R90FE]	3.9 uF [MDC15395K50B53 P3TUBE]	3.9 uH [SDR0906-3R9ML]
3.9 Ohm [CR0805-J/-3R9ELF]	3.9 Ohm [PWR4318W3R90JE]	3.9 uF [MDK15395K100B5 3P3TUBE]	3.9 uH [SDR1006-3R9ML]
3.9 Ohm [CR1206-J/-3R9ELF]	3.9 Ohm [PWR5322W3R90JE]	3.9 uF [MDS15395K100B5 3P3TUBE]	3.9 uH [SRN6028-3R9M]
3.9 Ohm [CR2010-J/-3R9ELF]	3.9 uF [35TQC3R9MYF]	3.9 uF [MDS15395K50B53 P3TUBE]	3.9 uH [SRP1040-3R9M]
3.9 Ohm [CRL0603-FW-3R90ELF]	3.9 uF [C1206C395K4RACT U]	3.9 uF [MMC12.7395K50B 31TR24]	3.9 uH [SRR0805-3R9M]
3.9 Ohm [CRL0603-JW-3R90ELF]	3.9 uF [C1206C395K8RACT U]	3.9 uH [SDE0604A-3R9M]	3.9 uH [SRR0908-3R9ML]
3.9 Ohm [CRL0805-FW-3R90ELF]	3.9 uF [C1206C395K9RACT U]	3.9 uH [SDE1006A-3R9M]	3.9 uH [SRR1003-3R9M]
3.9 Ohm [CRL0805-JW-3R90ELF]	3.9 uF [C1210C395K3NAC TU]	3.9 uH [SDR0302-3R9ML]	3.9 uH [SRR1240-3R9Y]
3.9 Ohm [CRL1206-FW-3R90ELF]	3.9 uF [MDC10395K100A5 2P3TUBE]	3.9 uH [SDR0403-3R9ML]	3.9 uH [SRR4018-3R9Y]
3.9 Ohm [CRL1206-JW-3R90ELF]	3.9 uF [MDC10395K50A52 P3TUBE]	3.9 uH [SDR0603-3R9ML]	3.9 uH [SRR4028-3R9Y]
3.9 Ohm [CRL2010-FW-3R90ELF]	3.9 uF [MDC15395K100B5 3P3TUBE]	3.9 uH [SDR0703-3R9ML]	3.9 uH [SRR5018-3R9Y]
3.9 Ohm [CRL2512-FW-3R90ELF]		3.9 uH [SDR0805-3R9ML]	3.9 uH [SRR6028-3R9Y]
3.9 Ohm [CRM2512-FX-3R90ELF]			3.9 uH [SRR7045-3R9M]
3.9 Ohm [CRM2512-JW-3R9ELF]			3.9 uH [SRU8043-3R9Y]
			3.92 kOhm [CR0402-FX-3921GLF]

Multisim 14.1 Base Edition Components

3.92 kOhm [CR0603-FX- 3921ELF]	30 kOhm [4306M- 102-303]	30 kOhm [CR0402- FX-3002GLF]	30 kOhm [CRT0805-BY- 3002ELF]
3.92 kOhm [CR0805-FX- 3921ELF]	30 kOhm [4308R- 102-303]	30 kOhm [CR0603- FX-3002ELF]	30 kOhm [CRT0805-FV- 3002ELF]
3.92 kOhm [CR1206-FX- 3921ELF]	30 kOhm [4308R- 102-303LF]	30 kOhm [CR0603- JW-303ELF]	30 kOhm [CRT1206-BY- 3002ELF]
3.92 kOhm [CRM1206-FX- 3921ELF]	30 kOhm [4310R- 101-303]	30 kOhm [CR0805- FX-3002ELF]	30 kOhm [PWR163S-25- 3002J]
3.92 kOhm [CRM1206-FX- 3921ELF]	30 kOhm [4310R- 101-303LF]	30 kOhm [CR0805- JW-303ELF]	30 kOhm [PWR220T-20- 3002F]
3.92 kOhm [CRT0603-BY- 3921ELF]	30 kOhm [4416P-1- 303]	30 kOhm [CR1206- FX-3002ELF]	30 kOhm [PWR220T-20- 3002J]
3.92 kOhm [CRT1206-BY- 3921ELF]	30 kOhm [4605X- 101-303LF]	30 kOhm [CR1206- JW-303ELF]	30 kOhm [PWR220T-20- 3002J]
3.92 Ohm [CRM1206-FX- 3R92ELF]	30 kOhm [4608X- 102-303LF]	30 kOhm [CR2010- FX-3002ELF]	30 kOhm [PWR221T-30- 3002F]
3_AMP	30 kOhm [4609X- 101-303LF]	30 kOhm [CR2010- JW-303ELF]	30 kOhm [PWR263S-20- 3002F]
30 GOhm [4116R- 1-309G]	30 kOhm [4814P-2- 303]	30 kOhm [CRM2512-FX- 3002ELF]	30 kOhm [PWR263S-20- 3002J]
30 GOhm [4116R- 1-309GLF]	30 kOhm [4814P-2- 303LF]	30 kOhm [CRM2512-JW- 303ELF]	30 kOhm [PWR263S-20- 3002J]
30 kOhm [4116R-1- 303]	30 kOhm [4816P-1- 303F]	30 kOhm [CRT0402-BY- 3002GLF]	30 kOhm [PWR263S-35- 3002F]
30 kOhm [4116R-1- 303LF]	30 kOhm [CAT16- 303J4LF]	30 kOhm [CRT0603-BY- 3002ELF]	30 kOhm [PWR263S-35- 3002J]
30 kOhm [4304M- 101-303]	30 kOhm [CAY16- 303J4LF]		
	30 kOhm [CR0201- FW-3002GLF]		

Multisim 14.1 Base Edition Components

30 mF [C0402C309K5GACT U]	30 mOhm [PWR163S-25- R030JE]	30 mOhm [PWR4412- 2SCR0300F]	30 Ohm [4816P- T01-300]
30 mF [C0805C309KBGAC TU]	30 mOhm [PWR1913WR030F]	30 mOhm [PWR4412- 2SCR0300J]	30 Ohm [4816P- T01-300LF]
30 mOhm [CRA2512-FZ- R030ELF]	30 mOhm [PWR1913WR030F E]	30 mOhm [PWR4412- 2SDR0300F]	30 Ohm [CAT10- 300J4LF]
30 mOhm [CRA2512-JZ- R030ELF]	30 mOhm [PWR1913WR030J]	30 mOhm [PWR4412- 2SDR0300J]	30 Ohm [CAT16- 30R0F4LF]
30 mOhm [CRF2512-FZ- R030ELF]	30 mOhm [PWR1913WR030JE]	30 mOhm [PWR4525WR030J]	30 Ohm [CAY10- 300J2LF]
30 mOhm [CRF2512-JZ- R030ELF]	30 mOhm [PWR221T-30- R030J]	30 mOhm [PWR4525WR030JE]	30 Ohm [CAY10- 300J4LF]
30 mOhm [CRL1206-FV- R030ELF]	30 mOhm [PWR2615WR030F]	30 mOhm [PWR6327WR030J]	30 Ohm [CAY16- 300J8LF]
30 mOhm [CRL1206-JV- R030ELF]	30 mOhm [PWR2615WR030F E]	30 mOhm [PWR6327WR030JE]	30 Ohm [CR0402- FX-30R0GLF]
30 mOhm [CRL2010-FV- R030ELF]	30 mOhm [PWR2615WR030J]	30 Ohm [4116R-1- 300]	30 Ohm [CR0402- JW-300GLF]
30 mOhm [CRL2010-JV- R030ELF]	30 mOhm [PWR2615WR030JE]	30 Ohm [4310M- 102-300]	30 Ohm [CR0603- FX-30R0ELF]
30 mOhm [CRL2512-FV- R030ELF]	30 mOhm [PWR4412- 2SBR0300F]	30 Ohm [4310M- 102-300LF]	30 Ohm [CR0603- JW-300ELF]
	30 mOhm [PWR4412- 2SBR0300J]	30 Ohm [4310R- 102-300LF]	30 Ohm [CR0805- FX-30R0ELF]
		30 Ohm [4608X- 102-300LF]	30 Ohm [CR0805- FX-30R0GLF]

Multisim 14.1 Base Edition Components

30 Ohm [CR0805-JW-300ELF]	30 Ohm [PWR220T-35-30R0J]	30 pF [C0805C300K5GACT U]	30.1 kOhm [CR0201-FW-3012GLF]
30 Ohm [CR1206-FX-30R0ELF]	30 Ohm [PWR221T-30-30R0J]	30 pF [C0805C300KBGAC TU]	30.1 kOhm [CR0402-FX-3012GLF]
30 Ohm [CR1206-JW-300ELF]	30 Ohm [PWR263S-20-30R0F]	30 pF [C1206C300K1GACT U]	30.1 kOhm [CR0603-FX-3012ELF]
30 Ohm [CRM2512-JW-300ELF]	30 Ohm [PWR263S-20-30R0J]	30 pF [C1206C300K5GACT U]	30.1 kOhm [CR0805-FX-3012ELF]
30 Ohm [CRT0805-FX-30R0ELF]	30 Ohm [PWR263S-35-30R0F]	30 pF [C1206C300KBGAC TU]	30.1 kOhm [CR1206-FX-3012ELF]
30 Ohm [PWR163S-25-30R0F]	30 Ohm [PWR263S-35-30R0J]	30 pF [C1210C300KBGAC TU]	30.1 kOhm [CRM2512-FX-3012ELF]
30 Ohm [PWR163S-25-30R0FE]	30 Ohm [PWR6327W30R0J]	30 pF [C1812C300KBGAC TU]	30.1 kOhm [CRT0603-BY-3012ELF]
30 Ohm [PWR163S-25-30R0J]	30 pF [C0402C300K5GACT U]	30 pF [C1825C300KBGAC TU]	30.1 kOhm [CRT0805-BW-3012ELF]
30 Ohm [PWR163S-25-30R0JE]	30 pF [C0603C300K2GACT U]	30 pF [C2220C300KBGAC TU]	30.1 kOhm [CRT0805-BY-3012ELF]
30 Ohm [PWR220T-20-30R0F]	30 pF [C0603C300K5GACT U]	30 pF [C2225C300KBGAC TU]	30.1 kOhm [CRT0805-FX-3012ELF]
30 Ohm [PWR220T-20-30R0J]	30 pF [C0805C300K2GACT U]	30.1 kOhm [CAT16-3012F4LF]	30.1 kOhm [CRT1206-BW-3012ELF]
		30.1 kOhm [CAY16-3012F4LF]	

Multisim 14.1 Base Edition Components

30.1 Ohm [CAT16-30R1F4LF]	30.9 kOhm [CR0805-FX-3092ELF]	300 kOhm [CR0201-FW-3003GLF]	300 mOhm [CRL0603-FW-R300ELF]
30.1 Ohm [CAY16-30R1F4LF]	30.9 kOhm [CR1206-FX-3092ELF]	300 kOhm [CR0402-FX-3003GLF]	300 mOhm [CRL0603-JW-R300ELF]
30.1 Ohm [CR0402-FX-30R1GLF]	30.9 kOhm [CRM2512-FX-3092ELF]	300 kOhm [CR0402-JW-304GLF]	300 mOhm [CRL0805-FW-R300ELF]
30.1 Ohm [CR0805-FX-30R1ELF]	30.9 kOhm [CRT0603-BY-3092ELF]	300 kOhm [CR0603-FX-3003ELF]	300 mOhm [CRL0805-JW-R300ELF]
30.1 Ohm [CR1206-FX-30R1ELF]	30.9 Ohm [CR0402-FX-30R9GLF]	300 kOhm [CR0603-JW-304ELF]	300 mOhm [CRL1206-FW-R300ELF]
30.1 Ohm [CR2010-FX-30R1ELF]	30.9 Ohm [CR0603-FX-30R9ELF]	300 kOhm [CR0805-FX-3003ELF]	300 mOhm [CRL1206-JW-R300ELF]
30.1 Ohm [CRM1206-FX-30R1ELF]	30.9 Ohm [CR0805-FX-30R9ELF]	300 kOhm [CR0805-JW-304ELF]	300 mOhm [CRL2010-FW-R300ELF]
30.1 Ohm [CRT0805-BY-30R1ELF]	30_AMP	300 kOhm [CR1206-FX-3003ELF]	300 mOhm [CRL2010-JW-R300ELF]
30.1 Ohm [CRT0805-DZ-30R1ELF]	300 kOhm [4116R-1-304LF]	300 kOhm [CR1206-JW-304ELF]	300 mOhm [CRL2512-FW-R300ELF]
30.1 Ohm [PWR2615N30R1F]	300 kOhm [4116R-2-304]	300 kOhm [CRS1206-FX-3003ELF]	300 mOhm [CRL2512-JW-R300ELF]
30.9 kOhm [CR0402-FX-3092GLF]	300 kOhm [4605X-101-304LF]	300 kOhm [CRT0603-BY-3003ELF]	300 mOhm [CRM2010-FX-R300ELF]
30.9 kOhm [CR0603-FX-3092ELF]	300 kOhm [CAY16-304J4LF]		

Multisim 14.1 Base Edition Components

300 mOhm [CRM2512-FX- R300ELF]	300 mOhm [PWR4525WR300JE]	300 Ohm [4308R- 102-301LF]	300 Ohm [CR0402- JW-301GLF]
300 mOhm [CRM2512-JX- R300ELF]	300 mOhm [PWR6327WR300J]	300 Ohm [4310R- 101-301]	300 Ohm [CR0603- FX-3000ELF]
300 mOhm [PWR163S-25- R300FE]	300 mOhm [PWR6327WR300JE]	300 Ohm [4310R- 101-301LF]	300 Ohm [CR0603- JW-301ELF]
300 mOhm [PWR1913WR300J]	300 Ohm [4114R-1- 301]	300 Ohm [4606X- 102-301LF]	300 Ohm [CR0805- FX-3000ELF]
300 mOhm [PWR1913WR300JE]	300 Ohm [4114R-2- 301]	300 Ohm [4608X- 102-301LF]	300 Ohm [CR0805- JW-301ELF]
300 mOhm [PWR220T-20- R300J]	300 Ohm [4116R-1- 301]	300 Ohm [4610X- 101-301LF]	300 Ohm [CR1206- FX-3000ELF]
300 mOhm [PWR221T-30- R300F]	300 Ohm [4116R-1- 301LF]	300 Ohm [4816P-1- 301]	300 Ohm [CR1206- JW-301ELF]
300 mOhm [PWR221T-30- R300J]	300 Ohm [4116R-2- 301]	300 Ohm [4816P- T02-301]	300 Ohm [CR2010- FX-3000ELF]
300 mOhm [PWR2615WR300J]	300 Ohm [4116R-2- 301LF]	300 Ohm [CAT16- 301J4LF]	300 Ohm [CR2010- JW-301ELF]
300 mOhm [PWR2615WR300JE]	300 Ohm [4306M- 102-301]	300 Ohm [CAT25- 301JALF]	300 Ohm [CR2512- JW-301ELF]
300 mOhm [PWR2615WR300JE]	300 Ohm [4306M- 102-301LF]	300 Ohm [CAY10- 301J4LF]	300 Ohm [CRT0402-FZ- 3000GLF]
300 mOhm [PWR263S-35- R300F]	300 Ohm [4306R- 101-301]	300 Ohm [CAY16- 3000F4LF]	300 Ohm [CRT0603-BZ- 3000ELF]
300 mOhm [PWR4525WR300J]	300 Ohm [4306R- 101-301LF]	300 Ohm [CAY16- 301J4LF]	300 Ohm [CRT0805-FX- 3000ELF]
	300 Ohm [4308R- 101-301]	300 Ohm [CR0201- JW-301GLF]	300 Ohm [CRT1206-BY- 3000ELF]
	300 Ohm [4308R- 102-301]	300 Ohm [CR0402- FX-3000GLF]	

Multisim 14.1 Base Edition Components

300 Ohm [PWR163S-25-3000FE]	300 pF [C1206C301K5GACTU]	301 Ohm [CAY16-3010F4LF]	309 kOhm [CR0805-FX-3093ELF]
300 Ohm [PWR221T-30-3000F]	300 pF [C1206C301KBGACTU]	301 Ohm [CR0402-FX-3010GLF]	309 kOhm [CR1206-FX-3093ELF]
300 Ohm [PWR263S-35-3000F]	300 pF [C1210C301KBGACTU]	301 Ohm [CR0603-FX-3010ELF]	309 Ohm [CR0402-FX-3090GLF]
300 Ohm [PWR263S-35-3000FE]	300 pF [C1812C301KBGACTU]	301 Ohm [CR1206-FX-3010ELF]	309 Ohm [CR0603-FX-3090ELF]
300 Ohm [PWR263S-35-3000J]	300 pF [C1825C301KBGACTU]	301 Ohm [CR2512-FX-3010ELF]	309 Ohm [CR0805-FX-3090ELF]
300 pF [C0402C301K1HACTU]	300 pF [C2220C301KBGACTU]	301 Ohm [CRM1206-FX-3010ELF]	309 Ohm [CR1206-FX-3090ELF]
300 pF [C0402C301K3HACTU]	300 pF [C2225C301KBGACTU]	301 Ohm [CRT0402-FZ-3010GLF]	30V_10W
300 pF [C0402C301K5HACTU]	301 kOhm [CR0402-FX-3013GLF]	301 Ohm [CRT0603-BV-3010ELF]	31.2 kOhm [CR1206-FX-3122ELF]
300 pF [C0805C301K1GACTU]	301 kOhm [CR0603-FX-3013ELF]	301 Ohm [CRT0603-BX-3010ELF]	31.6 kOhm [CR0201-FW-3162GLF]
300 pF [C0805C301K2GACTU]	301 kOhm [CR0805-FX-3013ELF]	301 Ohm [CRT0603-BY-3010ELF]	31.6 kOhm [CR0402-FX-3162GLF]
300 pF [C0805C301K5GACTU]	301 kOhm [CR1206-FX-3013ELF]	309 kOhm [CR0402-FX-3093GLF]	31.6 kOhm [CR0603-FX-3162ELF]
		309 kOhm [CR0603-FX-3093ELF]	31.6 kOhm [CR1206-FX-3162ELF]

Multisim 14.1 Base Edition Components

31.6 kOhm [CRT0402-FZ- 3162GLF]	316 Ohm [CR1206- FX-3160ELF]	32.4 Ohm [PWR6327W32R4F]	3280A
			3288RT
31.6 Ohm [CR0402- FX-31R6GLF]	316 Ohm [CRT0402-FZ- 3160GLF]	32.8 kOhm [CR1206-FX- 3282ELF]	33 kOhm [4114R-1- 333]
31.6 Ohm [CR0603- FX-31R6ELF]	32 kOhm [4609M- 101-323LF]	320 nH [SRP1270- R32M]	33 kOhm [4114R-1- 333LF]
31.6 Ohm [CR0805- FX-31R6ELF]	32.4 kOhm [CR0402-FX- 3242GLF]	324 kOhm [CR0402-FX- 3243GLF]	33 kOhm [4114R-2- 333]
31.6 Ohm [CR1206- FX-31R6ELF]	32.4 kOhm [CR0603-FX- 3242ELF]	324 kOhm [CR0603-FX- 3243ELF]	33 kOhm [4114R-2- 333LF]
31.6 Ohm [CRT0402-FZ- 31R6GLF]	32.4 kOhm [CR0805-FX- 3242ELF]	324 kOhm [CR0805-FX- 3243ELF]	33 kOhm [4116R-1- 333]
316 kOhm [CR0402-FX- 3163GLF]	32.4 kOhm [CR1206-FX- 3242ELF]	324 kOhm [CR1206-FX- 3243ELF]	33 kOhm [4116R-1- 333LF]
316 kOhm [CR0603-FX- 3163ELF]	32.4 kOhm [CR1206-FX- 3242ELF]	324 Ohm [CR0402- FX-3240GLF]	33 kOhm [4116R-2- 333]
316 kOhm [CR0805-FX- 3163ELF]	32.4 kOhm [CRT0603-BY- 3242ELF]	324 Ohm [CR0603- FX-3240ELF]	33 kOhm [4116R-2- 333LF]
316 kOhm [CR1206-FX- 3163ELF]	32.4 kOhm [CRT0805-FY- 3242ELF]	324 Ohm [CR0805- FX-3240ELF]	33 kOhm [4116R-2- 333LF]
316 Ohm [CR0402- FX-3160GLF]	32.4 Ohm [CR0402- FX-32R4GLF]	324 Ohm [CR1206- FX-3240ELF]	33 kOhm [4306H- 101-333]
316 Ohm [CR0603- FX-3160ELF]	32.4 Ohm [CR0603- FX-32R4ELF]	324 Ohm [CR0805- BV-3240ELF]	33 kOhm [4306H- 101-333LF]
316 Ohm [CR0805- FX-3160ELF]	32.4 Ohm [CR0805- FX-32R4ELF]	324 Ohm [CRT0805-BY- 3240ELF]	33 kOhm [4306R- 101-333]
	32.4 Ohm [CR1206- FX-32R4ELF]		33 kOhm [4306R- 102-333]
			33 kOhm [4306R- 102-333LF]

Multisim 14.1 Base Edition Components

33 kOhm [4308M-101-333]	33 kOhm [4310R-102-333LF]	33 kOhm [4607X-101-333LF]	33 kOhm [4814P-2-333]
33 kOhm [4308M-101-333LF]	33 kOhm [4416P-1-333LF]	33 kOhm [4608X-101-333LF]	33 kOhm [4814P-2-333LF]
33 kOhm [4308M-102-333]	33 kOhm [4416P-2-333]	33 kOhm [4608X-102-333LF]	33 kOhm [4814P-T01-333]
33 kOhm [4308M-102-333LF]	33 kOhm [4420P-2-333]	33 kOhm [4608X-AP1-333LF]	33 kOhm [4814P-T02-333]
33 kOhm [4308R-101-333]	33 kOhm [4420P-T01-333]	33 kOhm [4609M-101-333LF]	33 kOhm [4814P-T02-333LF]
33 kOhm [4308R-101-333LF]	33 kOhm [4420P-T02-333]	33 kOhm [4609X-101-333LF]	33 kOhm [4816P-1-333]
33 kOhm [4308R-102-333]	33 kOhm [4604X-101-333LF]	33 kOhm [4610M-101-333LF]	33 kOhm [4816P-1-333LF]
33 kOhm [4308R-102-333LF]	33 kOhm [4604X-102-333LF]	33 kOhm [4610X-101-333LF]	33 kOhm [4816P-2-333]
33 kOhm [4309R-101-333]	33 kOhm [4605X-101-333LF]	33 kOhm [4610X-102-333LF]	33 kOhm [4816P-2-333LF]
33 kOhm [4309R-101-333LF]	33 kOhm [4606H-101-333LF]	33 kOhm [4610X-AP1-333LF]	33 kOhm [4816P-T01-333]
33 kOhm [4310H-101-333]	33 kOhm [4606M-102-333LF]	33 kOhm [4611X-101-333LF]	33 kOhm [4816P-T01-333LF]
33 kOhm [4310H-101-333LF]	33 kOhm [4606X-101-333LF]	33 kOhm [4613X-101-333LF]	33 kOhm [4816P-T02-333]
33 kOhm [4310R-101-333]	33 kOhm [4606X-102-333LF]	33 kOhm [4614X-102-333LF]	33 kOhm [4816P-T02-333LF]
33 kOhm [4310R-101-333LF]	33 kOhm [4606X-AP1-333LF]	33 kOhm [4814P-1-333]	33 kOhm [4818P-T02-333]
33 kOhm [4310R-102-333]	33 kOhm [4606X-AP2-333LF]	33 kOhm [4814P-1-333LF]	33 kOhm [4820P-1-333]

Multisim 14.1 Base Edition Components

33 kOhm [4820P-1-333LF]	33 kOhm [CR0201-FW-3302GLF]	33 kOhm [CRM2512-JW-333ELF]	33 mOhm [PWR1913WR033F]
33 kOhm [4820P-2-333]	33 kOhm [CR0402-FX-3302GLF]	33 kOhm [CRT0402-CZ-3302GLF]	33 mOhm [PWR1913WR033F E]
33 kOhm [4820P-T01-333]	33 kOhm [CR0402-JW-333GLF]	33 kOhm [CRT0603-BY-3302ELF]	33 mOhm [PWR220T-20-R033J]
33 kOhm [4820P-T01-333LF]	33 kOhm [CR0603-FX-3302ELF]	33 kOhm [PWR220T-20-3302F]	33 mOhm [PWR221T-30-R033J]
33 kOhm [4820P-T02-333]	33 kOhm [CR0603-JW-333ELF]	33 mF [C0805C339KBGAC TU]	33 mOhm [PWR2615WR033F E]
33 kOhm [CAT10-333J4LF]	33 kOhm [CR0603-JW-333GLF]	33 mF [C1206C339K5GACT U]	33 nF [C0402C333K3RACT U]
33 kOhm [CAT16-3302F4LF]	33 kOhm [CR0805-FX-3302ELF]	33 mOhm [CRF2512-FZ-R033ELF]	33 nF [C0402C333K4RACT U]
33 kOhm [CAT16-333J4LF]	33 kOhm [CR0805-JW-333ELF]	33 mOhm [CRF2512-JZ-R033ELF]	33 nF [C0402C333K8PACT U]
33 kOhm [CAT16-333J8LF]	33 kOhm [CR0805-JW-333GLF]	33 mOhm [CRL2512-JV-R033ELF]	33 nF [C0402C333K8RACT U]
33 kOhm [CAT25-333JALF]	33 kOhm [CR1206-FX-3302ELF]	33 mOhm [PWR163S-25-R033J]	33 nF [C0402C333K9PACT U]
33 kOhm [CAY10-333J4LF]	33 kOhm [CR1206-JW-333ELF]	33 mOhm [PWR163S-25-R033JE]	33 nF [C0402C333K9RACT U]
33 kOhm [CAY16-3302F4LF]	33 kOhm [CR2010-JW-333ELF]		
33 kOhm [CAY16-333J4LF]	33 kOhm [CRM1206-JW-333ELF]		
33 kOhm [CAY16-333J8LF]	33 kOhm [CRM2512-FX-3302ELF]		
33 kOhm [CAY17-333JALF]			

Multisim 14.1 Base Edition Components

33 nF [C0603C333K1RACT U]	33 nF [C0805C333K4RACT U]	33 nF [C1206C333K3GACT U]	33 nF [C1210C333K3GACT U]
33 nF [C0603C333K3RACT U]	33 nF [C0805C333K5RACT U]	33 nF [C1206C333K3HACT U]	33 nF [C1210C333K3HACT U]
33 nF [C0603C333K4RACT U]	33 nF [C0805C333K8RACT U]	33 nF [C1206C333K5HACT U]	33 nF [C1210C333K5GACT U]
33 nF [C0603C333K5RACT U]	33 nF [C0805C333M5UAC TU]	33 nF [C1206C333K5RACT U]	33 nF [C1210C333K5HACT U]
33 nF [C0603C333K8RACT U]	33 nF [C0805F333K1RACT U]	33 nF [C1206C333KARACT U]	33 nF [C1210C333K5RACT U]
33 nF [C0603C333M3VAC TU]	33 nF [C0805F333K3RACT U]	33 nF [C1206C333M1UAC TU]	33 nF [C1210C333KARACT U]
33 nF [C0805C333K1RACT U]	33 nF [C0805F333K4RACT U]	33 nF [C1206C333M5UAC TU]	33 nF [C1812C333K1GACT U]
33 nF [C0805C333K2RACT U]	33 nF [C0805F333K5RACT U]	33 nF [C1210C333K1GACT U]	33 nF [C1812C333K1HACT U]
33 nF [C0805C333K3GACT U]	33 nF [C1206C333K1HACT U]	33 nF [C1210C333K1HACT U]	33 nF [C1812C333K1RACT U]
33 nF [C0805C333K3HACT U]	33 nF [C1206C333K1RACT U]	33 nF [C1210C333K1RACT U]	33 nF [C1812C333K2RACT U]
33 nF [C0805C333K3RACT U]	33 nF [C1206C333K2RACT U]	33 nF [C1210C333K2RACT U]	33 nF [C1812C333K5GACT U]

Multisim 14.1 Base Edition Components

33 nF [C1812C333K5HACT U]	33 nF [GMC7.3332K250K3 1TR12]	33 nF [MDC15333K400B5 3P3TUBE]	33 nF [MDS10333K400A5 2P3TUBE]
33 nF [C1812C333K5RACT U]	33 nF [GMC7.3332K63K31 TR12]	33 nF [MDC15333K50B53 P3TUBE]	33 nF [MDS10333K50A52 P3TUBE]
33 nF [C1825C333K1RACT U]	33 nF [GMC7.3333K63K31 TR12]	33 nF [MDC15333K630B5 3P3TUBE]	33 nF [MDS10333K630A5 2P3TUBE]
33 nF [C1825C333K5RACT U]	33 nF [GPC7.3333K63K33 TR12]	33 nF [MDK10333K100A5 2P3TUBE]	33 nF [MDS15333K100B5 3P3TUBE]
33 nF [C2220C333K1GACT U]	33 nF [MDC10333K100A5 2P3TUBE]	33 nF [MDK10333K250A5 2P3TUBE]	33 nF [MDS15333K250B5 3P3TUBE]
33 nF [C2220C333K2GACT U]	33 nF [MDC10333K250A5 2P3TUBE]	33 nF [MDK10333K400A5 2P3TUBE]	33 nF [MMC5.7333K50J3 1TR12]
33 nF [C2220C333K5GACT U]	33 nF [MDC10333K400A5 2P3TUBE]	33 nF [MDK10333K50A52 P3TUBE]	33 nF [MMC7.3333K250K 35TR12]
33 nF [C2225C333K5GACT U]	33 nF [MDC10333K50A52 P3TUBE]	33 nF [MDK15333K250B5 3P3TUBE]	33 nF [MMC7.3333K63K3 1TR12]
33 nF [CA064C333K4RACT U]	33 nF [MDC10333K630A5 2P3TUBE]	33 nF [MDK15333K630B5 3P3TUBE]	33 nF [SPC10.2333K100A 31TR16]
33 nF [GMC5.7332K250J3 1TR12]	33 nF [MDC15333K100B5 3P3TUBE]	33 nF [MDS10333K100A5 2P3TUBE]	33 nF [SPC10.2333K250A 31TR16]
33 nF [GMC5.7333K50J31 TR12]	33 nF [MDC15333K250B5 3P3TUBE]	33 nF [MDS10333K250A5 2P3TUBE]	33 nF [SPC12.7333K400B 31TR24]

Multisim 14.1 Base Edition Components

33 nF [SPC12.7333K630B 31TR24]	33 Ohm [4306R- 102-330]	33 Ohm [4310R- 101-330]	33 Ohm [4608H- 102-330LF]
33 nF [SPC7.3333K100K37 TR12]	33 Ohm [4306R- 102-330LF]	33 Ohm [4310R- 101-330LF]	33 Ohm [4608M- 102-330LF]
33 Ohm [4108R-1- 330]	33 Ohm [4308H- 102-330]	33 Ohm [4310R- 102-330]	33 Ohm [4608X- 101-330LF]
33 Ohm [4108R-1- 330LF]	33 Ohm [4308M- 102-330]	33 Ohm [4310R- 102-330LF]	33 Ohm [4608X- 102-330LF]
33 Ohm [4114R-1- 330]	33 Ohm [4308M- 102-330LF]	33 Ohm [4416P-1- 330]	33 Ohm [4608X- AP2-330LF]
33 Ohm [4114R-1- 330LF]	33 Ohm [4308R- 101-330]	33 Ohm [4416P-1- 330LF]	33 Ohm [4609X- 101-330LF]
33 Ohm [4114R-2- 330LF]	33 Ohm [4308R- 101-330LF]	33 Ohm [4416P- T01-330]	33 Ohm [4610H- 101-330LF]
33 Ohm [4116R-1- 330]	33 Ohm [4308R- 102-330]	33 Ohm [4416P- T01-330LF]	33 Ohm [4610X- 101-330LF]
33 Ohm [4116R-1- 330LF]	33 Ohm [4308R- 102-330LF]	33 Ohm [4416P- T02-330]	33 Ohm [4610X- 102-330LF]
33 Ohm [4116R-2- 330]	33 Ohm [4309R- 101-330]	33 Ohm [4420P-1- 330]	33 Ohm [4610X- AP2-330LF]
33 Ohm [4116R-2- 330LF]	33 Ohm [4310H- 101-330]	33 Ohm [4420P- T01-330]	33 Ohm [4612X- 102-330LF]
33 Ohm [4306M- 102-330]	33 Ohm [4310H- 101-330LF]	33 Ohm [4604X- 102-330LF]	33 Ohm [4614X- 102-330LF]
33 Ohm [4306M- 102-330LF]	33 Ohm [4310H- 102-330]	33 Ohm [4605X- 101-330LF]	33 Ohm [4814P-1- 330]
33 Ohm [4306R- 101-330]	33 Ohm [4310H- 102-330LF]	33 Ohm [4606X- 101-330LF]	33 Ohm [4814P-1- 330LF]
33 Ohm [4306R- 101-330LF]	33 Ohm [4310M- 102-330]	33 Ohm [4606X- 102-330LF]	33 Ohm [4814P- T01-330]

Multisim 14.1 Base Edition Components

33 Ohm [4814P-T01-330LF]	33 Ohm [CAT10-330J4LF]	33 Ohm [CR0201-FW-33R0GLF]	33 Ohm [CR2010-JW-330ELF]
33 Ohm [4814P-T02-330]	33 Ohm [CAT16-330J2LF]	33 Ohm [CR0201-JW-330GLF]	33 Ohm [CR2512-JW-330ELF]
33 Ohm [4816P-1-330]	33 Ohm [CAT16-330J4GLF]	33 Ohm [CR0402-FX-33R0GLF]	33 Ohm [CRM1206-FX-33R0ELF]
33 Ohm [4816P-1-330G]	33 Ohm [CAT16-330J4LF]	33 Ohm [CR0402-JW-330GLF]	33 Ohm [CRM1206-JW-330ELF]
33 Ohm [4816P-1-330LF]	33 Ohm [CAT16-330J8LF]	33 Ohm [CR0603-FX-33R0ELF]	33 Ohm [CRM2512-FX-33R0ELF]
33 Ohm [4816P-2-330]	33 Ohm [CAT16-33R0F4LF]	33 Ohm [CR0603-JW-330ELF]	33 Ohm [CRM2512-JW-330ELF]
33 Ohm [4816P-2-330LF]	33 Ohm [CAT16-33R0F8LF]	33 Ohm [CR0603-JW-330GLF]	33 Ohm [CRS1206-FX-33R0ELF]
33 Ohm [4816P-T01-330]	33 Ohm [CAT25-330JALF]	33 Ohm [CR0805-FX-33R0ELF]	33 Ohm [CRT0805-DZ-33R0ELF]
33 Ohm [4816P-T01-330LF]	33 Ohm [CAY10-330J2LF]	33 Ohm [CR0805-FX-33R0GLF]	33 Ohm [FW10A33R0JA]
33 Ohm [4816P-T02-330]	33 Ohm [CAY10-330J4LF]	33 Ohm [CR0805-JW-330ELF]	33 Ohm [FW20A33R0JA]
33 Ohm [4816P-T02-330LF]	33 Ohm [CAY16-330J4GLF]	33 Ohm [CR0805-JW-330GLF]	33 Ohm [FW30A33R0JA]
33 Ohm [4818P-T01-330]	33 Ohm [CAY16-330J4LF]	33 Ohm [CR1206-FX-33R0ELF]	33 Ohm [FW50A33R0JA]
33 Ohm [4820P-1-330]	33 Ohm [CAY16-330J8LF]	33 Ohm [CR1206-FX-33R0GLF]	33 Ohm [FW70A33R0JA]
33 Ohm [4820P-T01-330]	33 Ohm [CAY16-33R0F4LF]	33 Ohm [CR1206-JW-330ELF]	
33 Ohm [4820P-T01-330LF]	33 Ohm [CAY17-330JALF]	33 Ohm [CR2010-FX-33R0ELF]	

Multisim 14.1 Base Edition Components

33 Ohm [PWR163S-25-33R0F]	33 Ohm [PWR263S-20-33R0J]	33 pF [C0201C330K3GACT U]	33 pF [C0805C330K5GACT U]
33 Ohm [PWR163S-25-33R0J]	33 Ohm [PWR263S-35-33R0F]	33 pF [C0402C330K3GACT U]	33 pF [C0805C330KBGAC TU]
33 Ohm [PWR2010W33R0JE]	33 Ohm [PWR263S-35-33R0J]	33 pF [C0402C330K4GACT U]	33 pF [C0805C330KDGAC TU]
33 Ohm [PWR220T-20-33R0F]	33 Ohm [PWR263S-35-33R0JE]	33 pF [C0402C330K5GACT U]	33 pF [C1206C330K1GACT U]
33 Ohm [PWR220T-20-33R0J]	33 Ohm [PWR4318W33R0J]	33 pF [C0402C330K8GACT U]	33 pF [C1206C330K2GACT U]
33 Ohm [PWR220T-35-33R0J]	33 Ohm [PWR4318W33R0JE]	33 pF [C0603C330K1GACT U]	33 pF [C1206C330K5GACT U]
33 Ohm [PWR221T-30-33R0F]	33 Ohm [PWR4525W33R0J]	33 pF [C0603C330K2GACT U]	33 pF [C1206C330KBGAC TU]
33 Ohm [PWR221T-30-33R0J]	33 Ohm [W1M33R0J]	33 pF [C0603C330K3GACT U]	33 pF [C1206C330KCGAC TU]
33 Ohm [PWR2615W33R0F]	33 Ohm [WS1A33R0J]	33 pF [C0603C330K5GACT U]	33 pF [C1206C330KDGAC TU]
33 Ohm [PWR2615W33R0F E]	33 Ohm [WS1M33R0J]	33 pF [C0805C330K1GACT U]	33 pF [C1206C330KGGAC TU]
33 Ohm [PWR263S-20-33R0F]	33 Ohm [WS2M33R0J]	33 pF [C0805C330K2GACT U]	33 pF [C1210C330KBGAC TU]

Multisim 14.1 Base Edition Components

33 pF [C1812C330KBGAC TU]	33 uF [A700V336M006AT E025]	33 uF [EEFCX1D330R]	33 uF [T419E336M006AH 4250]
33 pF [C1825C330KBGAC TU]	33 uF [A700V336M006AT E028]	33 uF [EEFCX1E330R]	33 uF [T419X336M025AH 4250]
33 pF [C2220C330KBGAC TU]	33 uF [A700V336M008AT E018]	33 uF [EEFHX1D330R]	33 uF [T489D336M020AT E250]
33 pF [C2225C330KBGAC TU]	33 uF [A700V336M008AT E025]	33 uF [EEFHX1E330R]	33 uF [T491A336M003AT]
33 pF [CA064C330K5GAC TU]	33 uF [A700V336M008AT E028]	33 uF [EEHZA1E330R]	33 uF [T491A336M004AT]
33 pF [CA064C330K8GAC TU]	33 uF [A700V336M010AT E018]	33 uF [EEHZA1J330P]	33 uF [T491A336M010AT]
33 uF [10TPB33M]	33 uF [A700V336M010AT E025]	33 uF [EEHZA1K330P]	33 uF [T491B336M004AT]
33 uF [12TPG33M]	33 uF	33 uF [EEHZC1E330R]	33 uF [T491B336M006AT]
33 uF [16TQC33MYFD]	33 uF [A700V336M010AT E028]	33 uF [EEHZC1H330XP]	33 uF [T491B336M010AT]
33 uF [16TQC33MYFS]	33 uF [ATPH33MAHA]	33 uF [EEHZC1J330P]	33 uF [T491B336M016AT]
33 uF [20SVP33M]	33 uF [EEFCS1C330R]	33 uF [T409F336M004AH 4250]	33 uF [T491C336M004AT]
33 uF [25TQC33MYF]	33 uF [EEFCT1D330R]	33 uF [T409G336M010AH 4250]	33 uF [T491C336M006AT]
33 uF [A700V336M006AT E018]	33 uF [EEFCX1C330R]		33 uF [T491C336M010AT]

Multisim 14.1 Base Edition Components

33 uF [T491C336M016AT]	33 uF [T491U336M010AT]	33 uF [T494C336M010AT]	33 uF [T494U336M006AT]
33 uF [T491C336M020AT]	33 uF [T491U336M016AT]	33 uF [T494C336M016AT]	33 uF [T494U336M010AT]
33 uF [T491C336M025AT]	33 uF [T491V336M010AT]	33 uF [T494C336M020AT]	33 uF [T494U336M016AT]
33 uF [T491D336M010AT]	33 uF [T491V336M020AT]	33 uF [T494D336M010AT]	33 uF [T494V336M010AT]
33 uF [T491D336M016AT]	33 uF [T491X336M025AT]	33 uF [T494D336M016AT]	33 uF [T494V336M020AT]
33 uF [T491D336M020AT]	33 uF [T491X336M035AT]	33 uF [T494D336M020AT]	33 uF [T494X336M025AT]
33 uF [T491D336M025AT]	33 uF [T494A336M003AT]	33 uF [T494D336M025AT]	33 uF [T495B336M010AT E450]
33 uF [T491D336M035AT]	33 uF [T494A336M004AT]	33 uF [T494D336M035AT]	33 uF [T495C336M016AT E200]
33 uF [T491T336M004AT]	33 uF [T494B336M004AT]	33 uF [T494T336M004AT]	33 uF [T495D336M016AT E225]
33 uF [T491T336M006AT]	33 uF [T494B336M006AT]	33 uF [T494T336M006AT]	33 uF [T495D336M020AT E100]
33 uF [T491U336M004AT]	33 uF [T494C336M004AT]	33 uF [T494U336M004AT]	
33 uF [T491U336M006AT]	33 uF [T494C336M006AT]		

Multisim 14.1 Base Edition Components

33 uF [T495D336M020AT E200]	33 uF [T495X336M035AT E100]	33 uF [T520A336M004AT E080]	33 uF [T520B336M010AT E035]
33 uF [T495D336M025AT E090]	33 uF [T495X336M035AT E175]	33 uF [T520A336M006AT E070]	33 uF [T520B336M010AT E040]
33 uF [T495D336M025AT E100]	33 uF [T495X336M035AT E250]	33 uF [T520A336M006AT E080]	33 uF [T520B336M010AT E070]
33 uF [T495D336M025AT E225]	33 uF [T497H336M015AT 6110]	33 uF [T520B336M006AT E025]	33 uF [T520C336M006AT E100]
33 uF [T495D336M025AT E300]	33 uF [T498B336M006AT E1K7]	33 uF [T520B336M006AT E035]	33 uF [T520T336M006AT E070]
33 uF [T495E336M035AT E200]	33 uF [T498D336M016AT E600]	33 uF [T520B336M006AT E040]	33 uF [T520T336M008AT E070]
33 uF [T495V336M010AT E100]	33 uF [T498D336M025AT E600]	33 uF [T520B336M006AT E070]	33 uF [T520T336M008AT E080]
33 uF [T495V336M010AT E150]	33 uF [T498X336M035AT E500]	33 uF [T520B336M008AT E025]	33 uF [T520T336M010AT E070]
33 uF [T495X336M025AT E100]	33 uF [T510X336M035AT E050]	33 uF [T520B336M008AT E035]	33 uF [T520T336M010AT E080]
33 uF [T495X336M025AT E175]	33 uF [T510X336M035AT E065]	33 uF [T520B336M008AT E040]	33 uF [T520U336M008AT E070]
33 uF [T495X336M025AT E200]	33 uF [T520A336M004AT E070]	33 uF [T520B336M008AT E070]	33 uF [T520U336M010AT E070]

Multisim 14.1 Base Edition Components

33 uF [T520V336M016AT E045]	33 uF [T528I336M010ATE 150]	33 uF [TAJB336K016RNJ]	33 uF [TAJV336K035RNJ]
33 uF [T520V336M016AT E060]	33 uF [T541X336M050AH 6510]	33 uF [TAJC336K006RNJ]	33 uF [TAJW336K006RNJ]
33 uF [T520V336M016AT E070]	33 uF [T543A336M004AT E070]	33 uF [TAJC336K016RNJ]	33 uF [TAJW336K016RNJ]
33 uF [T520W336M016AT E045]	33 uF [T543B336M010AT E040]	33 uF [TAJC336K020RNJ]	33 uF [TAJY336K016RNJ]
33 uF [T521D336M025AT E060]	33 uF [TACR336K002RTA]	33 uF [TAJD336K010RNJ]	33 uF [TAJY336K020RNJ]
33 uF [T521D336M035AT E065]	33 uF [TACR336K003RTA]	33 uF [TAJD336K016RNJ]	33 uF [TAJY336K025RNJ]
33 uF [T521V336M025AT E060]	33 uF [TACR336K004RTA]	33 uF [TAJD336K020RNJ]	33 uF [THJB336K006RJN]
33 uF [T525B336M006AT E080]	33 uF [TACR336K006RTA]	33 uF [TAJD336K025RNJ]	33 uF [THJC336K010RJN]
33 uF [T525B336M010AT E080]	33 uF [TAJA336K004RNJ]	33 uF [TAJD336K035RNJ]	33 uF [THJC336K016RJN]
33 uF [T525T336M008AT E080]	33 uF [TAJA336K006RNJ]	33 uF [TAJE336K025RNJ]	33 uF [THJD336K020RJN]
33 uF [T525T336M010AT E080]	33 uF [TAJA336K010RNJ]	33 uF [TAJE336K035RNJ]	33 uF [THJE336K035RJN]
33 uF [T525T336M008AT E080]	33 uF [TAJB336K004RNJ]	33 uF [TAJP336K002RNJ]	33 uF [TPME336K035R00 50]
33 uF [T525T336M010AT E080]	33 uF [TAJB336K006RNJ]	33 uF [TAJS336K004RNJ]	33 uF [TPME336K035R00 65]
	33 uF [TAJB336K010RNJ]		

Multisim 14.1 Base Edition Components

33 uF [TPSA336K006R060 0]	33 uF [TPSC336K016R030 0]	33 uF [TPSE336K025R017 5]	33 uF [TPSW336K016R05 00]
33 uF [TPSB336K006R045 0]	33 uF [TPSC336K020R030 0]	33 uF [TPSE336K025R020 0]	33 uF [TPSY336K016R030 0]
33 uF [TPSB336K006R060 0]	33 uF [TPSD336K016R020 0]	33 uF [TPSE336K025R030 0]	33 uF [TPSY336K016R040 0]
33 uF [TPSB336K010R025 0]	33 uF [TPSD336K020R010 0]	33 uF [TPSE336K035R010 0]	33 uF [TRJB336K006RRJ]
33 uF [TPSB336K010R042 5]	33 uF [TPSD336K020R020 0]	33 uF [TPSE336K035R025 0]	33 uF [TRJB336K010RRJ]
33 uF [TPSB336K010R050 0]	33 uF [TPSD336K025R010 0]	33 uF [TPSE336K035R030 0]	33 uF [TRJC336K010RRJ]
33 uF [TPSB336K010R065 0]	33 uF [TPSD336K025R020 0]	33 uF [TPST336K006R080 0]	33 uF [TRJE336K035RRJ]
33 uF [TPSC336K010R015 0]	33 uF [TPSD336K025R030 0]	33 uF [TPSW336K010R03 50]	33 uF [TRMD336K025R00 65]
33 uF [TPSC336K010R037 5]	33 uF [TPSD336K035R020 0]	33 uF [TPSW336K016R01 75]	33 uF [TRME336K035R00 65]
33 uF [TPSC336K010R050 0]	33 uF [TPSD336K035R030 0]	33 uF [TPSW336K016R02 50]	33 uH [SDE0403A- 330K]
33 uF [TPSC336K016R022 5]	33 uF [TPSE336K025R010 0]	33 uF [TPSW336K016R04 00]	33 uH [SDE0604A- 330M]
			33 uH [SDE0805A- 330M]

Multisim 14.1 Base Edition Components

33 uH [SDE1006A-330M]	33 uH [SDR1307-330KL]	33 uH [SRN8040-330M]	33 uH [SRR1205-330ML]
33 uH [SDR0302-330KL]	33 uH [SDR1307A-330K]	33 uH [SRP1038A-330M]	33 uH [SRR1206-330YL]
33 uH [SDR0403-330KL]	33 uH [SDR1806-330ML]	33 uH [SRP1770TA-330M]	33 uH [SRR1208-330YL]
33 uH [SDR0503-330KL]	33 uH [SDR6603-330M]	33 uH [SRR0603-330KL]	33 uH [SRR1210-330M]
33 uH [SDR0603-330KL]	33 uH [SDR7030-330M]	33 uH [SRR0604-330KL]	33 uH [SRR1210A-330M]
33 uH [SDR0604-330KL]	33 uH [SDR7045-330M]	33 uH [SRR0618-330ML]	33 uH [SRR1240-330M]
33 uH [SDR0703-330KL]	33 uH [SRN1060-330M]	33 uH [SRR0735A-330M]	33 uH [SRR1260-330M]
33 uH [SDR0805-330KL]	33 uH [SRN3010-330M]	33 uH [SRR0745A-330M]	33 uH [SRR1260A-330M]
33 uH [SDR0906-330KL]	33 uH [SRN3015-330M]	33 uH [SRR0804-330Y]	33 uH [SRR1280-330M]
33 uH [SDR1005-330KL]	33 uH [SRN4018-330M]	33 uH [SRR0805-330Y]	33 uH [SRR1806-330M]
33 uH [SDR1006-330KL]	33 uH [SRN4026-330M]	33 uH [SRR0905-330Y]	33 uH [SRR3011-330YL]
33 uH [SDR1030-330M]	33 uH [SRN5020-330M]	33 uH [SRR0906-330ML]	33 uH [SRR4011-330YL]
33 uH [SDR1045-330M]	33 uH [SRN5040-330M]	33 uH [SRR0908-330ML]	33 uH [SRR4018-330Y]
33 uH [SDR1105-330KL]	33 uH [SRN6028-330M]	33 uH [SRR1003-330M]	33 uH [SRR4028-330Y]
33 uH [SDR1305-330M]	33 uH [SRN6045-330M]	33 uH [SRR1005-330Y]	33 uH [SRR5018-330Y]

Multisim 14.1 Base Edition Components

33 uH [SRR5028-330Y]	33 uH [SRU2013-330Y]	33 uH [SRU8028A-330Y]	33.2 kOhm [CRT0805-DZ-3322ELF]
33 uH [SRR6028-330Y]	33 uH [SRU2016-330Y]	33 uH [SRU8043-330Y]	33.2 kOhm [CRT1206-FZ-3322ELF]
33 uH [SRR6038-330Y]	33 uH [SRU3017-330Y]	33.2 kOhm [CAY16-3322F4LF]	33.2 Ohm [CAT16-33R2F4LF]
33 uH [SRR6040A-330M]	33 uH [SRU3028-330Y]	33.2 kOhm [CR0402-FX-3322GLF]	33.2 Ohm [CAY16-33R2F4LF]
33 uH [SRR6603-330ML]	33 uH [SRU3028A-330Y]	33.2 kOhm [CR0603-FX-3322ELF]	33.2 Ohm [CR0402-FX-33R2GLF]
33 uH [SRR7032-330M]	33 uH [SRU5011-330Y]	33.2 kOhm [CR0805-FX-3322ELF]	33.2 Ohm [CR0603-FX-33R2ELF]
33 uH [SRR7045-330M]	33 uH [SRU5016-330Y]	33.2 kOhm [CR1206-FX-3322ELF]	33.2 Ohm [CR0805-FX-33R2ELF]
33 uH [SRU1028-330Y]	33 uH [SRU5018-330Y]	33.2 kOhm [CR2512-FX-3322ELF]	33.2 Ohm [CR1206-FX-33R2ELF]
33 uH [SRU1028A-330Y]	33 uH [SRU5028-330Y]	33.2 kOhm [CRM2512-FX-3322ELF]	33.2 Ohm [CRM1206-FX-33R2ELF]
33 uH [SRU1038-330Y]	33 uH [SRU5028A-330Y]	33.2 kOhm [CRT0402-FZ-3322GLF]	33.2 Ohm [CRT0402-FZ-33R2GLF]
33 uH [SRU1038A-330Y]	33 uH [SRU6011-330Y]	33.2 kOhm [CRT0603-BX-3322ELF]	330 kOhm [4114R-1-334]
33 uH [SRU1048-330Y]	33 uH [SRU6018-330Y]	33.2 kOhm [CRT0805-BY-3322ELF]	330 kOhm [4114R-1-334LF]
33 uH [SRU1048A-330Y]	33 uH [SRU6025-330Y]		330 kOhm [4116R-1-334]
33 uH [SRU1063-330Y]	33 uH [SRU6025A-330Y]		
33 uH [SRU2011-330Y]	33 uH [SRU8028-330Y]		

Multisim 14.1 Base Edition Components

330 kOhm [4116R-1-334LF]	330 kOhm [4310R-102-334]	330 kOhm [4816P-1-334]	330 kOhm [CAY16-334J4LF]
330 kOhm [4116R-2-334]	330 kOhm [4310R-102-334LF]	330 kOhm [4816P-1-334LF]	330 kOhm [CAY16-334J8LF]
330 kOhm [4116R-2-334LF]	330 kOhm [4420P-2-334]	330 kOhm [4816P-2-334]	330 kOhm [CHV0603-JW-334ELF]
330 kOhm [4306M-102-334]	330 kOhm [4420P-T02-334]	330 kOhm [4816P-2-334LF]	330 kOhm [CHV0805-JW-334ELF]
330 kOhm [4306R-101-334]	330 kOhm [4604X-102-334LF]	330 kOhm [4816P-T01-334]	330 kOhm [CR0402-FX-3303GLF]
330 kOhm [4306R-101-334LF]	330 kOhm [4605X-101-334LF]	330 kOhm [4816P-T01-334LF]	330 kOhm [CR0603-FX-3303ELF]
330 kOhm [4306R-102-334]	330 kOhm [4606M-101-334LF]	330 kOhm [4816P-T02-334]	330 kOhm [CR0603-JW-334ELF]
330 kOhm [4306R-102-334LF]	330 kOhm [4606X-101-334LF]	330 kOhm [4816P-T02-334LF]	330 kOhm [CR0805-FX-3303ELF]
330 kOhm [4308R-101-334]	330 kOhm [4606X-102-334LF]	330 kOhm [4820P-T02-334]	330 kOhm [CR0805-JW-334ELF]
330 kOhm [4308R-101-334LF]	330 kOhm [4608X-101-334LF]	330 kOhm [CAT10-334J4LF]	330 kOhm [CR0805-FX-3303ELF]
330 kOhm [4308R-102-334]	330 kOhm [4608X-102-334LF]	330 kOhm [CAT16-3303F4LF]	330 kOhm [CR0805-JW-334ELF]
330 kOhm [4308R-102-334LF]	330 kOhm [4609X-101-334LF]	330 kOhm [CAT16-334J4LF]	330 kOhm [CR0805-JW-334GLF]
330 kOhm [4309R-101-334]	330 kOhm [4610X-101-334LF]	330 kOhm [CAT25-334J4LF]	330 kOhm [CR1206-FX-3303ELF]
330 kOhm [4310R-101-334]	330 kOhm [4610X-102-334LF]	330 kOhm [CAY10-334J4LF]	330 kOhm [CR1206-JW-334ELF]
330 kOhm [4310R-101-334LF]	330 kOhm [4612X-101-334LF]	330 kOhm [CAY16-3303F4LF]	

Multisim 14.1 Base Edition Components

330 kOhm [CR1206-JW-334GLF]	330 mOhm [CRL2512-FW-R330ELF]	330 nF [C0603C334K8RACTU]	330 nF [C1206C334K4RACTU]
330 kOhm [CRT0805-BY-3303ELF]	330 mOhm [CRL2512-JW-R330ELF]	330 nF [C0603C334K9RACTU]	330 nF [C1206C334K5RACTU]
330 kOhm [CRT1206-BY-3303ELF]	330 mOhm [CRM1206-FX-R330ELF]	330 nF [C0805C334K3NACTU]	330 nF [C1206C334M3VACTU]
330 mOhm [CRL0603-FW-R330ELF]	330 mOhm [CRM2512-FX-R330ELF]	330 nF [C0805C334K3RACTU]	330 nF [C1206F334K3RACTU]
330 mOhm [CRL0603-JW-R330ELF]	330 mOhm [PWR163S-25-R330FE]	330 nF [C0805C334K4RACTU]	330 nF [C1206F334K4RACTU]
330 mOhm [CRL0805-FW-R330ELF]	330 mOhm [PWR221T-30-R330F]	330 nF [C0805C334K8RACTU]	330 nF [C1210C334K1RACTU]
330 mOhm [CRL0805-JW-R330ELF]	330 mOhm [PWR263S-20-R330J]	330 nF [C0805C334M3VACTU]	330 nF [C1210C334K3RACTU]
330 mOhm [CRL1206-FW-R330ELF]	330 mOhm [PWR263S-35-R330F]	330 nF [C0805C334M4VACTU]	330 nF [C1210C334K5RACTU]
330 mOhm [CRL1206-JW-R330ELF]	330 nF [C0603C334K4PACTU]	330 nF [C0805C334M8VACTU]	330 nF [C1210C334M5UACTU]
330 mOhm [CRL2010-FW-R330ELF]	330 nF [C0603C334K4RACTU]	330 nF [C1206C334K1RACTU]	330 nF [C1210C334M5VACTU]
330 mOhm [CRL2010-JW-R330ELF]	330 nF [C0603C334K8PACTU]	330 nF [C1206C334K3RACTU]	330 nF [C1210F334K1RACTU]

Multisim 14.1 Base Edition Components

330 nF [C1210F334K3RACT U]	330 nF [C1825C334K1RACT U]	330 nF [C2225C334K5RACT U]	330 nF [MDC15334K400B5 5P3TUBE]
330 nF [C1210F334K4RACT U]	330 nF [C1825C334K2RACT U]	330 nF [C2225C334M5UAC TU]	330 nF [MDC15334K400B5 5P4TUBE]
330 nF [C1210F334K5RACT U]	330 nF [C1825C334K5RACT U]	330 nF [GMC7.3334K63K35 TR12]	330 nF [MDC15334K50B53 P3TUBE]
330 nF [C1812C334K1RACT U]	330 nF [C1825C334M5UAC TU]	330 nF [LG224Z334MAT2S 1]	330 nF [MDK10334K100A5 2P3TUBE]
330 nF [C1812C334K5RACT U]	330 nF [C2220C334K1GACT U]	330 nF [MDC10334K100A5 2P3TUBE]	330 nF [MDK10334K250A5 2P3TUBE]
330 nF [C1812C334KARACT U]	330 nF [C2220C334K1RACT U]	330 nF [MDC10334K250A5 2P3TUBE]	330 nF [MDK10334K50A52 P3TUBE]
330 nF [C1812C334M5UAC TU]	330 nF [C2220C334K2RACT U]	330 nF [MDC10334K400A5 7P7TUBE]	330 nF [MDS10334K100A5 2P3TUBE]
330 nF [C1812F334K1RACT U]	330 nF [C2220C334K5GACT U]	330 nF [MDC10334K400A5 7P8TUBE]	330 nF [MDS10334K250A5 2P3TUBE]
330 nF [C1812F334K2RACT U]	330 nF [C2220C334K5RACT U]	330 nF [MDC10334K50A52 P3TUBE]	330 nF [MDS10334K50A52 P3TUBE]
330 nF [C1812F334K3RACT U]	330 nF [C2225C334K1RACT U]	330 nF [MDC15334K100B5 3P3TUBE]	330 nF [MDS15334K100B5 3P3TUBE]
330 nF [C1812F334K5RACT U]	330 nF [C2225C334K2RACT U]	330 nF [MDC15334K250B5 3P3TUBE]	330 nF [MDS15334K250B5 3P3TUBE]

Multisim 14.1 Base Edition Components

330 nF [PG224D334MAB2S 1]	330 nF [TAJA334K035RNJ]	330 nH [SRP1265A- R33M]	330 Ohm [4116R-2- 331LF]
330 nF [PG224W334MAB2 S1]	330 nF [TAJB334K050RNJ]	330 nH [SRP4020TA-R33M]	330 Ohm [4306H- 101-331]
330 nF [PG224Z334MAB2S 1]	330 nF [TAJR334K020RNJ]	330 nH [SRP5015TA-R33M]	330 Ohm [4306H- 101-331LF]
330 nF [SPC16.5334K100C 31TR24]	330 nF [TAJR334K035RNJ]	330 nH [SRP5030T- R33M]	330 Ohm [4306H- 102-331]
330 nF [SPC16.5334K250C 31TR24]	330 nF [TAJS334K020RNJ]	330 nH [SRP7028A- R33M]	330 Ohm [4306M- 101-331]
330 nF [T409A334M025AH 4250]	330 nF [TAJS334K035RNJ]	330 nH [SRP7030- R33FM]	330 Ohm [4306M- 102-331]
330 nF [T491A334M025AT]	330 nF [THJA334K035RJN]	330 nH [SRP7050TA-R33M]	330 Ohm [4306R- 101-331]
330 nF [T491A334M035AT]	330 nF [TPSA334K035R600 0]	330 Ohm [4114R-1- 331]	330 Ohm [4306R- 101-331LF]
330 nF [T491B334M050AT]	330 nF [W2L1ZC334MAT1A]	330 Ohm [4114R-1- 331LF]	330 Ohm [4306R- 102-331]
330 nF [T494A334M025AT]	330 nF [W3L1YC334MAT1A]	330 Ohm [4114R-2- 331]	330 Ohm [4306R- 102-331LF]
330 nF [T494A334M035AT]	330 nH [SRN2512- R33M]	330 Ohm [4114R-2- 331LF]	330 Ohm [4308H- 101-331]
330 nF [T494B334M050AT]	330 nH [SRP1235- R33M]	330 Ohm [4116R-1- 331]	330 Ohm [4308H- 102-331]
330 nF [T496B334M050AT 6110]	330 nH [SRP1245A- R33M]	330 Ohm [4116R-1- 331LF]	330 Ohm [4308H- 102-331LF]
		330 Ohm [4116R-2- 331]	330 Ohm [4308M- 101-331]

Multisim 14.1 Base Edition Components

330 Ohm [4308M-101-331LF]	330 Ohm [4310R-101-331]	330 Ohm [4420P-T02-331]	330 Ohm [4608X-AP2-331LF]
330 Ohm [4308M-102-331]	330 Ohm [4310R-101-331LF]	330 Ohm [4604X-101-331LF]	330 Ohm [4609X-101-331LF]
330 Ohm [4308M-102-331LF]	330 Ohm [4310R-102-331]	330 Ohm [4604X-102-331LF]	330 Ohm [4609X-AP1-331LF]
330 Ohm [4308R-101-331]	330 Ohm [4310R-102-331LF]	330 Ohm [4605X-101-331LF]	330 Ohm [4610H-101-331LF]
330 Ohm [4308R-101-331LF]	330 Ohm [4311R-101-331]	330 Ohm [4605X-AP1-331LF]	330 Ohm [4610H-102-331LF]
330 Ohm [4308R-102-331]	330 Ohm [4416P-1-331]	330 Ohm [4606H-101-331LF]	330 Ohm [4610M-101-331LF]
330 Ohm [4308R-102-331LF]	330 Ohm [4416P-1-331LF]	330 Ohm [4606M-101-331LF]	330 Ohm [4610X-101-331LF]
330 Ohm [4309R-101-331]	330 Ohm [4416P-2-331]	330 Ohm [4606X-101-331LF]	330 Ohm [4610X-102-331LF]
330 Ohm [4309R-101-331LF]	330 Ohm [4416P-T01-331]	330 Ohm [4606X-102-331LF]	330 Ohm [4611X-101-331LF]
330 Ohm [4310H-101-331]	330 Ohm [4416P-T01-331LF]	330 Ohm [4606X-AP1-331LF]	330 Ohm [4612X-102-331LF]
330 Ohm [4310H-101-331LF]	330 Ohm [4416P-T02-331]	330 Ohm [4607X-101-331LF]	330 Ohm [4614X-102-331LF]
330 Ohm [4310M-101-331]	330 Ohm [4420P-1-331]	330 Ohm [4608H-102-331LF]	330 Ohm [4814P-1-331]
330 Ohm [4310M-101-331LF]	330 Ohm [4420P-2-331]	330 Ohm [4608M-102-331LF]	330 Ohm [4814P-1-331LF]
330 Ohm [4310M-102-331]	330 Ohm [4420P-2-331LF]	330 Ohm [4608X-101-331LF]	330 Ohm [4814P-2-331]
330 Ohm [4310M-102-331LF]	330 Ohm [4420P-T01-331]	330 Ohm [4608X-102-331LF]	330 Ohm [4814P-2-331LF]

Multisim 14.1 Base Edition Components

330 Ohm [4814P-T01-331]	330 Ohm [4820P-2-331]	330 Ohm [CAY16-331J4LF]	330 Ohm [CR1206-JW-331ELF]
330 Ohm [4814P-T01-331LF]	330 Ohm [4820P-T01-331]	330 Ohm [CAY16-331J8LF]	330 Ohm [CR1206-JW-331GLF]
330 Ohm [4814P-T02-331]	330 Ohm [4820P-T01-331LF]	330 Ohm [CAY17-331JALF]	330 Ohm [CR2010-JW-331ELF]
330 Ohm [4814P-T02-331LF]	330 Ohm [4820P-T02-331]	330 Ohm [CR0201-JW-331GLF]	330 Ohm [CR2512-FX-3300ELF]
330 Ohm [4816P-1-331]	330 Ohm [4820P-T02-331LF]	330 Ohm [CR0402-FX-3300GLF]	330 Ohm [CR2512-JW-331ELF]
330 Ohm [4816P-1-331LF]	330 Ohm [CAT10-331J4LF]	330 Ohm [CR0402-JW-331GLF]	330 Ohm [CRM2512-FX-3300ELF]
330 Ohm [4816P-2-331]	330 Ohm [CAT16-3300F4LF]	330 Ohm [CR0603-FX-3300ELF]	330 Ohm [CRT0603-BY-3300ELF]
330 Ohm [4816P-2-331F]	330 Ohm [CAT16-3300F8LF]	330 Ohm [CR0603-FX-3300GLF]	330 Ohm [CRT0603-FY-3300ELF]
330 Ohm [4816P-2-331LF]	330 Ohm [CAT16-331J2LF]	330 Ohm [CR0603-JW-331ELF]	330 Ohm [PWR163S-25-3300FE]
330 Ohm [4816P-T01-331]	330 Ohm [CAT16-331J4GLF]	330 Ohm [CR0603-JW-331GLF]	330 Ohm [PWR220T-20-3300F]
330 Ohm [4816P-T01-331LF]	330 Ohm [CAT16-331J4LF]	330 Ohm [CR0805-FX-3300ELF]	330 Ohm [PWR220T-20-3300J]
330 Ohm [4816P-T02-331]	330 Ohm [CAT16-331J8LF]	330 Ohm [CR0805-FX-3300GLF]	330 Ohm [PWR220T-35-3300J]
330 Ohm [4816P-T02-331LF]	330 Ohm [CAT25-331JALF]	330 Ohm [CR0805-JW-331ELF]	
330 Ohm [4820P-1-331]	330 Ohm [CAY10-331J4LF]	330 Ohm [CR0805-JW-331GLF]	
330 Ohm [4820P-1-331LF]	330 Ohm [CAY16-3300F4LF]	330 Ohm [CR1206-FX-3300ELF]	

Multisim 14.1 Base Edition Components

330 Ohm [PWR263S-20-3300F]	330 pF [C0402C331K4GACT U]	330 pF [C0603C331K5GACT U]	330 pF [C0805C331K5RACT U]
330 Ohm [PWR263S-20-3300J]	330 pF [C0402C331K4RACT U]	330 pF [C0603C331K5RACT U]	330 pF [C0805C331K8RACT U]
330 Ohm [PWR263S-20-3300JE]	330 pF [C0402C331K5GACT U]	330 pF [C0603C331K8RACT U]	330 pF [C1206C331K1GACT U]
330 Ohm [PWR263S-35-3300F]	330 pF [C0402C331K5HACT U]	330 pF [C0805C331K1GACT U]	330 pF [C1206C331K2GACT U]
330 Ohm [PWR263S-35-3300J]	330 pF [C0402C331K5RACT U]	330 pF [C0805C331K1RACT U]	330 pF [C1206C331K5GACT U]
330 Ohm [PWR263S-35-3300JE]	330 pF [C0402C331K8RACT U]	330 pF [C0805C331K2GACT U]	330 pF [C1206C331KBGAC TU]
330 Ohm [PWR5322W3300FE]	330 pF [C0603C331K1RACT U]	330 pF [C0805C331K2RACT U]	330 pF [C1206C331KCGAC TU]
330 Ohm [PWR6327W3300J]	330 pF [C0603C331K2RACT U]	330 pF [C0805C331K3GACT U]	330 pF [C1210C331K1GACT U]
330 Ohm [PWR6327W330RJ]	330 pF [C0603C331K3GACT U]	330 pF [C0805C331K3RACT U]	330 pF [C1210C331K5GACT U]
330 pF [C0402C331K1HACT U]	330 pF [C0603C331K3RACT U]	330 pF [C0805C331K4RACT U]	330 pF [C1210C331KBGAC TU]
330 pF [C0402C331K3HACT U]	330 pF [C0603C331K4RACT U]	330 pF [C0805C331K5GACT U]	330 pF [C1812C331KBGAC TU]
330 pF [C0402C331K3RACT U]			

Multisim 14.1 Base Edition Components

330 pF [C1825C331KBGAC TU]	330 uF [2R5TPE330MAZB]	330 uF [4TPF330ML]	330 uF [A700X337M002AT E015]
330 pF [C2220C331KBGAC TU]	330 uF [2R5TPE330MC]	330 uF [6SVPC330M]	330 uF [A700X337M004AT E010]
330 pF [C2225C331KBGAC TU]	330 uF [2R5TPE330MF]	330 uF [6TPB330M]	330 uF [A700X337M004AT E015]
330 pF [CA064C331K5GAC TU]	330 uF [2R5TPF330M7L]	330 uF [6TPB330ML]	330 uF [A700X337M2R5AT E010]
330 pF [CA064C331K5RACT U]	330 uF [2SEPC330MW]	330 uF [6TPC330MA]	330 uF [A700X337M2R5AT E015]
330 uF [10TPB330M]	330 uF [2TPE330MAFB]	330 uF [6TPE330MAL]	330 uF [EEFCX0D331R]
330 uF [10TPE330M]	330 uF [2TPE330MFB]	330 uF [6TPE330MAP]	330 uF [EEFCX0D331XR]
330 uF [16SVP330M]	330 uF [2TPF330M6]	330 uF [6TPE330MFL]	330 uF [EEFCX0E331R]
330 uF [2R5SVPE330M]	330 uF [4SVPC330M]	330 uF [6TPE330MIL]	330 uF [EEFCX0G331R]
330 uF [2R5SVPE330MY]	330 uF [4SVPC330MV]	330 uF [6TPE330ML]	330 uF [EEFGX0D331R]
330 uF [2R5TPE330M]	330 uF [4SVPC330MY]	330 uF [6TPF330M9L]	330 uF [EEFHX0E331R]
330 uF [2R5TPE330M7]	330 uF [4TPB330ML]	330 uF [A700D337M002AT E007]	330 uF [EEFHX0E331R4]
330 uF [2R5TPE330M9]	330 uF [4TPE330M]	330 uF [A700X337M002AT E010]	330 uF [EEFHX0E331R6]
	330 uF [4TPE330MI]		

Multisim 14.1 Base Edition Components

330 uF [EEFH0E331R9]	330 uF [T489X337M010AT E100]	330 uF [T494D337M010AT]	330 uF [T495D337M010AT E125]
330 uF [EEFLT0D331R]	330 uF [T491C337M004AT]	330 uF [T494E337M006AT]	330 uF [T495D337M010AT E150]
330 uF [EEFLX0D331R]	330 uF [T491D337M004AT]	330 uF [T494E337M010AT]	330 uF [T495E337M010AT E060]
330 uF [EEFLX0D331R4]	330 uF [T491D337M006AT]	330 uF [T494V337M004AT]	330 uF [T495X337M006AT E045]
330 uF [EEFLX0E331R]	330 uF [T491D337M010AT]	330 uF [T494X337M006AT]	330 uF [T495X337M006AT E065]
330 uF [EEFLX0E331R4]	330 uF [T491D337M010AT]	330 uF [T494X337M010AT]	330 uF [T495X337M006AT E100]
330 uF [EEFST0D331R]	330 uF [T491E337M006AT]	330 uF [T495D337M004AT E030]	330 uF [T495X337M006AT E100]
330 uF [EEFSX0D331E4]	330 uF [T491E337M010AT]	330 uF [T495D337M006AT E040]	330 uF [T495X337M010AT E035]
330 uF [EEFSX0D331ER]	330 uF [T491V337M004AT]	330 uF [T495D337M006AT E050]	330 uF [T495X337M010AT E050]
330 uF [EEFSX0D331XE]	330 uF [T491X337M006AT]	330 uF [T495D337M006AT E070]	330 uF [T495X337M010AT E060]
330 uF [EEFSX0E331E4]	330 uF [T491X337M010AT]	330 uF [T495D337M006AT E100]	330 uF [T495X337M010AT E100]
330 uF [EEFSX0E331ER]	330 uF [T494C337M004AT]	330 uF [T495D337M006AT E100]	330 uF [T495X337M010AT E035]
330 uF [EEFSX0E331XE]	330 uF [T494D337M004AT]	330 uF [T495D337M010AT E100]	
330 uF [EEHZA1E331P]	330 uF [T494D337M006AT]		
330 uF [EEHZC1E331P]			

Multisim 14.1 Base Edition Components

330 uF [T513X337M010AH 6110]	330 uF [T520D337M004AT E015]	330 uF [T520L337M2R5AT E009]	330 uF [T520V337M004AT E025]
330 uF [T520B337M2R5AT E045]	330 uF [T520D337M004AT E040]	330 uF [T520L337M2R5AT E012]	330 uF [T520V337M004AT E040]
330 uF [T520B337M2R5AT E070]	330 uF [T520D337M004AT E045]	330 uF [T520L337M2R5AT E025]	330 uF [T520V337M006AT E015]
330 uF [T520C337M004AT E025]	330 uF [T520D337M006AT E009]	330 uF [T520V337M003AT E009]	330 uF [T520V337M006AT E025]
330 uF [T520C337M2R5AT E015]	330 uF [T520D337M006AT E010]	330 uF [T520V337M003AT E012]	330 uF [T520V337M006AT E040]
330 uF [T520C337M2R5AT E025]	330 uF [T520D337M006AT E015]	330 uF [T520V337M003AT E015]	330 uF [T520V337M2R5AT E006]
330 uF [T520C337M2R5AT E045]	330 uF [T520D337M006AT E025]	330 uF [T520V337M003AT E025]	330 uF [T520V337M2R5AT E007]
330 uF [T520D337M004AT E006]	330 uF [T520D337M006AT E040]	330 uF [T520V337M004AT E007]	330 uF [T520V337M2R5AT E009]
330 uF [T520D337M004AT E007]	330 uF [T520D337M006AT E045]	330 uF [T520V337M004AT E009]	330 uF [T520V337M2R5AT E012]
330 uF [T520D337M004AT E009]	330 uF [T520D337M2R5AT E006]	330 uF [T520V337M004AT E012]	330 uF [T520V337M2R5AT E015]
330 uF [T520D337M004AT E012]	330 uF [T520D337M2R5AT E007]	330 uF [T520V337M004AT E018]	330 uF [T520V337M2R5AT E018]

Multisim 14.1 Base Edition Components

330 uF [T520V337M2R5AT E025]	330 uF [T520Y337M010AT E035]	330 uF [T528Z337M2R5AT E008]	330 uF [T541X337M010AH 6520]
330 uF [T520V337M2R5AT E040]	330 uF [T522V337M006AT E040]	330 uF [T528Z337M2R5AT E009]	330 uF [T541Y337M006AH 6510]
330 uF [T520W337M2R5A TE025]	330 uF [T525D337M003AT E025]	330 uF [T528Z337M2R5AT E012]	330 uF [T543C337M2R5AT E045]
330 uF [T520W337M2R5A TE040]	330 uF [T525D337M004AT E025]	330 uF [T530D337M004AT E006]	330 uF [T543L337M2R5AT E025]
330 uF [T520X337M010AT E010]	330 uF [T525D337M006AT E025]	330 uF [T530D337M006AT E006]	330 uF [T543Y337M006AT E015]
330 uF [T520X337M010AT E025]	330 uF [T525D337M006AT E040]	330 uF [T530D337M006AT E010]	330 uF [TAJC337K004RNJ]
330 uF [T520X337M010AT E040]	330 uF [T525D337M2R5AT E025]	330 uF [T530X337M010AT E004]	330 uF [TAJC337K006RNJ]
330 uF [T520Y337M006AT E015]	330 uF [T528Z337M004AT E009]	330 uF [T530X337M010AT E005]	330 uF [TAJD337K004RNJ]
330 uF [T520Y337M006AT E025]	330 uF [T528Z337M004AT E012]	330 uF [T530X337M010AT E006]	330 uF [TAJD337K010RNJ]
330 uF [T520Y337M006AT E040]	330 uF [T528Z337M2R5AT E005]	330 uF [T530X337M010AT E010]	330 uF [TAJE337K006RNJ]
330 uF [T520Y337M010AT E015]	330 uF [T528Z337M2R5AT E007]	330 uF [T530Y337M006AT E006]	330 uF [TAJE337K010RNJ]
			330 uF [TAJV337K010RNJ]

Multisim 14.1 Base Edition Components

330 uF [TAJY337K006RNJ]	330 uF [TPSD337K006R010 0]	330 uF [TPSV337K010R004 0]	330 uH [SDR0503- 331KL]
330 uF [TPME337K010R00 23]	330 uF [TPSD337K010R010 0]	330 uF [TPSV337K010R006 0]	330 uH [SDR0603- 331KL]
330 uF [TPME337K010R00 35]	330 uF [TPSD337K010R015 0]	330 uF [TPSV337K010R010 0]	330 uH [SDR0604- 331KL]
330 uF [TPSC337K006R008 0]	330 uF [TPSE337K006R005 0]	330 uF [TPSY337K006R015 0]	330 uH [SDR0703- 331KL]
330 uF [TPSC337K006R010 0]	330 uF [TPSE337K006R010 0]	330 uF [TRJD337K006RRJ]	330 uH [SDR0805- 331KL]
330 uF [TPSD337K004R003 5]	330 uF [TPSE337K006R012 5]	330 uF [TRJE337K006RRJ]	330 uH [SDR0906- 331KL]
330 uF [TPSD337K004R004 5]	330 uF [TPSE337K006R015 0]	330 uF [TRJE337K010RRJ]	330 uH [SDR1005- 331KL]
330 uF [TPSD337K004R010 0]	330 uF [TPSE337K010R004 0]	330 uF [TRMD337K004R00 35]	330 uH [SDR1006- 331KL]
330 uF [TPSD337K006R004 5]	330 uF [TPSE337K010R005 0]	330 uF [TRME337K010R00 35]	330 uH [SDR1030- 331K]
330 uF [TPSD337K006R005 0]	330 uF [TPSE337K010R006 0]	330 uH [SDE0805A- 331K]	330 uH [SDR1045- 331K]
330 uF [TPSD337K006R007 0]	330 uF [TPSE337K010R010 0]	330 uH [SDE1006A- 331K]	330 uH [SDR1305- 331K]
		330 uH [SDR0302- 331KL]	330 uH [SDR1307- 331KL]
		330 uH [SDR0403- 331KL]	330 uH [SDR1307A-331K]
			330 uH [SDR1806- 331KL]
			330 uH [SDR6603- 331M]

Multisim 14.1 Base Edition Components

330 uH [SDR7030-331K]	330 uH [SRR1206-331KL]	330 uH [SRU1038-331Y]	332 Ohm [CR0402-FX-3320GLF]
330 uH [SDR7045-331K]	330 uH [SRR1208-331KL]	330 uH [SRU1038A-331Y]	332 Ohm [CR0603-FX-3320ELF]
330 uH [SRN1060-331M]	330 uH [SRR1210-331M]	330 uH [SRU1048-331Y]	332 Ohm [CR0603-FX-3320GLF]
330 uH [SRR0603-331KL]	330 uH [SRR1210A-331M]	330 uH [SRU1048A-331Y]	332 Ohm [CR0805-FX-3320ELF]
330 uH [SRR0604-331KL]	330 uH [SRR1240-331K]	332 kOhm [CAY16-3323F4LF]	332 Ohm [CR1206-FX-3320ELF]
330 uH [SRR0735A-331M]	330 uH [SRR1260-331K]	332 kOhm [CR0402-FX-3323GLF]	332 Ohm [CRM2512-FX-3320ELF]
330 uH [SRR0745A-331M]	330 uH [SRR1260A-331K]	332 kOhm [CR0603-FX-3323ELF]	332 Ohm [CRT0402-FZ-3320GLF]
330 uH [SRR0804-331K]	330 uH [SRR1280-331K]	332 kOhm [CR0805-FX-3323ELF]	332 Ohm [CRT1206-FZ-3320ELF]
330 uH [SRR0805-331K]	330 uH [SRR1806-331M]	332 kOhm [CR1206-FX-3323ELF]	34 kOhm [4816P-1-343]
330 uH [SRR0905-331K]	330 uH [SRR4028-331Y]	332 kOhm [CRT0603-BY-3323ELF]	34 kOhm [4816P-1-343LF]
330 uH [SRR0906-331YL]	330 uH [SRR5028-331Y]	332 kOhm [CRT1206-DY-3323ELF]	34 kOhm [CR0402-FX-3402GLF]
330 uH [SRR0908-331YL]	330 uH [SRR6028-331Y]	332 kOhm [CRT1206-FZ-3323ELF]	34 kOhm [CR0603-FX-3402ELF]
330 uH [SRR1003-331Y]	330 uH [SRR6603-331ML]	332 kOhm [CR0805-FX-3402ELF]	34 kOhm [CR1206-FX-3402ELF]
330 uH [SRR1005-331K]	330 uH [SRR7032-331M]	332 Ohm [CAY16-3320F4LF]	
330 uH [SRR1205-331KL]	330 uH [SRR7045-331M]		

Multisim 14.1 Base Edition Components

34 mOhm [CRA2512-JZ- R034ELF]	34.8 Ohm [CR0805- FX-34R8ELF]	340 Ohm [CRM1206-FX- 3400ELF]	35.7 kOhm [CR0603-FX- 3572ELF]
34 Ohm [CR0603- FX-34R0ELF]	34.8 Ohm [CR1206- FX-34R8ELF]	348 kOhm [CR0402-FX- 3483GLF]	35.7 kOhm [CR0805-FX- 3572ELF]
34 Ohm [CR0805- FX-34R0ELF]	34.8 Ohm [CRM2010-FX- 34R8ELF]	348 kOhm [CR0603-FX- 3483ELF]	35.7 kOhm [CR1206-FX- 3572ELF]
34 Ohm [CR1206- FX-34R0ELF]	340 kOhm [CR0402-FX- 3403GLF]	348 kOhm [CR0805-FX- 3483ELF]	35.7 kOhm [CRM2512-FX- 3572ELF]
34.8 kOhm [CAT16- 3482F4LF]	340 kOhm [CR0603-FX- 3403ELF]	348 kOhm [CR1206-FX- 3483ELF]	35.7 Ohm [CR0402- FX-35R7GLF]
34.8 kOhm [CR0402-FX- 3482GLF]	340 kOhm [CR0805-FX- 3403ELF]	348 kOhm [CRM2512-FX- 3483ELF]	35.7 Ohm [CR0603- FX-35R7ELF]
34.8 kOhm [CR0603-FX- 3482ELF]	340 kOhm [CR1206-FX- 3403ELF]	348 Ohm [CR0402- FX-3480GLF]	35.7 Ohm [CR0805- FX-35R7ELF]
34.8 kOhm [CR0805-FX- 3482ELF]	340 kOhm [CRT0603-BY- 3403ELF]	348 Ohm [CR0603- FX-3480ELF]	35.7 Ohm [CR1206- FX-35R7ELF]
34.8 kOhm [CR1206-FX- 3482ELF]	340 kOhm [CRT1206-BY- 3403ELF]	348 Ohm [CR0805- FX-3480ELF]	3-534206-0
34.8 kOhm [CRM2512-FX- 3482ELF]	340 Ohm [CR0603- FX-3400ELF]	348 Ohm [CR1206- FX-3480ELF]	3554AM
34.8 kOhm [CRT0603-BX- 3482ELF]	340 Ohm [CR0805- FX-3400ELF]	35 mOhm [CRF2512-FZ- R035ELF]	3554BM
34.8 Ohm [CR0402- FX-34R8GLF]	340 Ohm [CR1206- FX-3400ELF]	35.7 kOhm [CR0402-FX- 3572GLF]	3554SM
34.8 Ohm [CR0603- FX-34R8ELF]			357 kOhm [CR0402-FX- 3573GLF]
			357 kOhm [CR0603-FX- 3573ELF]

Multisim 14.1 Base Edition Components

357 kOhm [CR0805-FX-3573ELF]	36 kOhm [CR0201-FW-3602GLF]	36 mOhm [PWR4525WR036JE]	36 Ohm [CR0603-FX-36R0ELF]
357 kOhm [CR1206-FX-3573ELF]	36 kOhm [CR0402-FX-3602GLF]	36 mOhm [PWR6327WR036J]	36 Ohm [CR0603-JW-360ELF]
357 Ohm [CR0402-FX-3570GLF]	36 kOhm [CR0603-FX-3602ELF]	36 mOhm [PWR6327WR036JE]	36 Ohm [CR0603-JW-360GLF]
357 Ohm [CR0603-FX-3570ELF]	36 kOhm [CR0603-JW-363ELF]	36 Ohm [4116R-1-360]	36 Ohm [CR0805-FX-36R0ELF]
357 Ohm [CR0805-FX-3570ELF]	36 kOhm [CR0805-FX-3602ELF]	36 Ohm [4116R-1-360L]	36 Ohm [CR0805-JW-360ELF]
357 Ohm [CR0805-FX-3570GLF]	36 kOhm [CR0805-JW-363ELF]	36 Ohm [4116R-1-360LF]	36 Ohm [CR1206-FX-36R0ELF]
357 Ohm [CR1206-FX-3570ELF]	36 kOhm [CR1206-FX-3602ELF]	36 Ohm [4816P-1-360]	36 Ohm [CR1206-JW-360ELF]
357 Ohm [CR1206-FX-3570ELF]	36 kOhm [CR1206-JW-363ELF]	36 Ohm [CAT10-360J4LF]	36 Ohm [CR1206-JW-360ELF]
357 Ohm [CR2010-FX-3570ELF]	36 mF [C0805C369KBGAC TU]	36 Ohm [CAT16-360J4LF]	36 Ohm [CART0805-BW-36R0ELF]
357 Ohm [CR2512-FX-3570ELF]	36 mOhm [PWR1913WR036J]	36 Ohm [CAT16-360J4LF]	36 Ohm [PWR6327N36R0JE]
357 Ohm [CRT1206-BY-3570ELF]	36 mOhm [PWR1913WR036JE]	36 Ohm [CAY10-360J2LF]	36 pF [C0805C360KBGAC TU]
36 kOhm [4308R-102-363LF]	36 mOhm [PWR2615WR036J]	36 Ohm [CAY10-360J4LF]	36 pF [C1206C360KBGAC TU]
36 kOhm [4310R-101-363]	36 mOhm [PWR2615WR036JE]	36 Ohm [CAY16-360J4LF]	36 pF [C1210C360KBGAC TU]
36 kOhm [4604X-102-363LF]	36 mOhm [PWR4525WR036J]	36 Ohm [CAY16-36R0F4LF]	36 pF [C1812C360KBGAC TU]
36 kOhm [CAY16-363J4LF]		36 Ohm [CAY17-360J4LF]	
		36 Ohm [CR0402-FX-36R0GLF]	
		36 Ohm [CR0402-JW-360GLF]	

Multisim 14.1 Base Edition Components

36 pF [C1825C360KBGAC TU]	36.5 Ohm [CR1206- FX-36R5ELF]	360 kOhm [CR0805-JW- 364ELF]	360 mOhm [CRL2512-FW- R360ELF]
36 pF [C2220C360KBGAC TU]	36.5 Ohm [PWR1913W36R5F]	360 kOhm [CR1206-FX- 3603ELF]	360 mOhm [CRL2512-JW- R360ELF]
36 pF [C2220C360KZGACT U]	36.5 Ohm [PWR1913W36R5F E]	360 kOhm [CR1206-JW- 364ELF]	360 mOhm [CRM1206-FX- R360ELF]
36 pF [C2225C360KBGAC TU]	36.5 Ohm [PWR2010W36R5F E]	360 mOhm [CRL0603-FW- R360ELF]	360 mOhm [PWR1913WR360J]
36.5 kOhm [CR0402-FX- 3652GLF]	360 kOhm [4114R- 1-364]	360 mOhm [CRL0603-JW- R360ELF]	360 mOhm [PWR1913WR360JE]
36.5 kOhm [CR0603-FX- 3652ELF]	360 kOhm [CAY16- 364J4LF]	360 mOhm [CRL0805-FW- R360ELF]	360 mOhm [PWR2615WR360J]
36.5 kOhm [CR0805-FX- 3652ELF]	360 kOhm [CHV0805-FX- 3603ELF]	360 mOhm [CRL0805-JW- R360ELF]	360 mOhm [PWR2615WR360JE]
36.5 kOhm [CR1206-FX- 3652ELF]	360 kOhm [CR0402-FX- 3603GLF]	360 mOhm [CRL1206-FW- R360ELF]	360 mOhm [PWR4525WR360J]
36.5 Ohm [CAY16- 36R5F4LF]	360 kOhm [CR0603-FX- 3603ELF]	360 mOhm [CRL1206-JW- R360ELF]	360 mOhm [PWR4525WR360JE]
36.5 Ohm [CR0402- FX-36R5GLF]	360 kOhm [CR0603-JW- 364ELF]	360 mOhm [CRL2010-FW- R360ELF]	360 mOhm [PWR6327WR360J]
36.5 Ohm [CR0603- FX-36R5ELF]	360 kOhm [CR0805-FX- 3603ELF]	360 mOhm [CRL2010-JW- R360ELF]	360 nH [SRP1038A- R36M]
36.5 Ohm [CR0805- FX-36R5ELF]			360 nH [SRP1040- R36M]

Multisim 14.1 Base Edition Components

360 nH [SRP1045-R36Y]	360 Ohm [CR0402-JW-361GLF]	360 pF [C1206C361KBGAC TU]	365 Ohm [CAY16-3650F4LF]
360 nH [SRP1250-R36M]	360 Ohm [CR0603-FX-3600ELF]	360 pF [C1210C361KBGAC TU]	365 Ohm [CR0402-FX-3650GLF]
360 nH [SRP4012TA-R36M]	360 Ohm [CR0603-JW-361ELF]	360 pF [C1812C361KBGAC TU]	365 Ohm [CR0603-FX-3650ELF]
360 nH [SRP4020-R36M]	360 Ohm [CR0805-FX-3600ELF]	360 pF [C1825C361KBGAC TU]	365 Ohm [CR0805-FX-3650ELF]
360 Ohm [4116R-1-361]	360 Ohm [CR0805-JW-361ELF]	360 pF [C2220C361KBGAC TU]	365 Ohm [CR1206-FX-3650ELF]
360 Ohm [4116R-1-361LF]	360 Ohm [CR1206-FX-3600ELF]	360 pF [C2225C361KBGAC TU]	365 Ohm [CRT0402-FZ-3650GLF]
360 Ohm [4310R-101-361]	360 Ohm [CR1206-JW-361ELF]	360 pF [C2225C361KBGAC TU]	37.4 kOhm [CR0402-FX-3742GLF]
360 Ohm [4608X-102-361LF]	360 Ohm [CR2010-JW-361ELF]	3-644456-5	37.4 kOhm [CR0603-FX-3742ELF]
360 Ohm [4610X-101-361LF]	360 Ohm [PWR163S-25-3600FE]	3-644456-8	37.4 kOhm [CR0603-FX-3742GLF]
360 Ohm [4814P-T01-361]	360 pF [C0402C361K1HACT U]	365 kOhm [CR0402-FX-3653GLF]	37.4 kOhm [CR0805-FX-3742ELF]
360 Ohm [4816P-2-361]	360 pF [C0402C361K3HACT U]	365 kOhm [CR0603-FX-3653ELF]	37.4 kOhm [CR1206-FX-3742ELF]
360 Ohm [4816P-2-361LF]	360 pF [C0402C361K5HACT U]	365 kOhm [CR0805-FX-3653ELF]	37.4 kOhm [CRT1206-BY-3742ELF]
360 Ohm [CAT16-361J4LF]	360 pF [C0603C361K5GACT U]	365 kOhm [CR1206-FX-3653ELF]	37.4 Ohm [CAT16-37R4F4LF]
360 Ohm [CAY16-361J4LF]			
360 Ohm [CR0402-FX-3600GLF]			

Multisim 14.1 Base Edition Components

37.4 Ohm [CR0402-FX-37R4GLF]	38 Ohm [4116R-1-380LF]	38.3 Ohm [CRT0402-FZ-38R3GLF]	383 Ohm [CRT0402-BW-3830GLF]
37.4 Ohm [CR0603-FX-37R4ELF]	38.3 kOhm [CR0402-FX-3832GLF]	383 kOhm [CR0402-FX-3833GLF]	39 kOhm [4114R-1-393]
37.4 Ohm [CR0805-FX-37R4ELF]	38.3 kOhm [CR0603-FX-3832ELF]	383 kOhm [CR0603-FX-3833ELF]	39 kOhm [4114R-1-393LF]
37.4 Ohm [CR0805-FX-37R4GLF]	38.3 kOhm [CR0805-FX-3832ELF]	383 kOhm [CR0805-FX-3833ELF]	39 kOhm [4116R-1-393]
37.4 Ohm [CR1206-FX-37R4ELF]	38.3 kOhm [CR1206-FX-3832ELF]	383 kOhm [CR1206-FX-3833ELF]	39 kOhm [4116R-1-393LF]
374 kOhm [CR0402-FX-3743GLF]	38.3 kOhm [CR1206-FX-3832ELF]	383 kOhm [CR0805-FX-3833GLF]	39 kOhm [4116R-2-393]
374 kOhm [CR0603-FX-3743ELF]	38.3 kOhm [CRT0402-FZ-3832GLF]	383 kOhm [CR1206-FX-3833ELF]	39 kOhm [4116R-2-393LF]
374 kOhm [CR0805-FX-3743ELF]	38.3 kOhm [CRT0603-BY-3832ELF]	383 kOhm [CRT1206-BY-3833ELF]	39 kOhm [4306M-102-393]
374 kOhm [CR1206-FX-3743ELF]	38.3 kOhm [CRT0805-BY-3832ELF]	383 Ohm [CR0402-FX-3830GLF]	39 kOhm [4306R-101-393]
374 Ohm [CR0402-FX-3740GLF]	38.3 Ohm [CR0402-FX-38R3GLF]	383 Ohm [CR0603-FX-3830ELF]	39 kOhm [4306R-101-393LF]
374 Ohm [CR0603-FX-3740ELF]	38.3 Ohm [CR0603-FX-38R3ELF]	383 Ohm [CR0805-FX-3830ELF]	39 kOhm [4306R-102-393]
374 Ohm [CR0805-FX-3740ELF]	38.3 Ohm [CR0805-FX-38R3ELF]	383 Ohm [CR1206-FX-3830ELF]	39 kOhm [4306R-102-393LF]
374 Ohm [CR1206-FX-3740ELF]	38.3 Ohm [CR1206-FX-38R3ELF]	383 Ohm [CRM2512-FX-3830ELF]	39 kOhm [4308M-102-393]
38 Ohm [4116R-1-380]			39 kOhm [4308M-102-393LF]

Multisim 14.1 Base Edition Components

39 kOhm [4308R-101-393]	39 kOhm [4608M-101-393LF]	39 kOhm [4816P-T02-393LF]	39 kOhm [CR0603-JW-393ELF]
39 kOhm [4308R-101-393LF]	39 kOhm [4608M-102-393LF]	39 kOhm [4820P-2-393F]	39 kOhm [CR0603-JW-393GLF]
39 kOhm [4308R-102-393]	39 kOhm [4608X-101-393LF]	39 kOhm [CAT10-393J4LF]	39 kOhm [CR0805-FX-3902ELF]
39 kOhm [4308R-102-393LF]	39 kOhm [4608X-102-393LF]	39 kOhm [CAT16-3902F4LF]	39 kOhm [CR0805-JW-393ELF]
39 kOhm [4309R-101-393LF]	39 kOhm [4609H-101-393LF]	39 kOhm [CAT16-393J4LF]	39 kOhm [CR0805-JW-393GLF]
39 kOhm [4310R-101-393]	39 kOhm [4609X-101-393LF]	39 kOhm [CAT25-393JALF]	39 kOhm [CR1206-FX-3902ELF]
39 kOhm [4310R-101-393LF]	39 kOhm [4610X-101-393LF]	39 kOhm [CAY10-393J2LF]	39 kOhm [CR1206-JW-393ELF]
39 kOhm [4310R-102-393]	39 kOhm [4610X-102-393LF]	39 kOhm [CAY10-393J4LF]	39 mF [C0805C399KBGAC TU]
39 kOhm [4310R-102-393LF]	39 kOhm [4816P-1-393]	39 kOhm [CAY16-3902F4LF]	39 mOhm [PWR1913WR039F]
39 kOhm [4420P-2-393]	39 kOhm [4816P-1-393LF]	39 kOhm [CAY16-393J4LF]	39 mOhm [PWR1913WR039F E]
39 kOhm [4604X-102-393LF]	39 kOhm [4816P-2-393]	39 kOhm [CAY16-393J8LF]	39 mOhm [PWR2615WR039F]
39 kOhm [4606M-102-393LF]	39 kOhm [4816P-2-393LF]	39 kOhm [CAY17-393JALF]	39 mOhm [PWR2615WR039F E]
39 kOhm [4606X-101-393LF]	39 kOhm [4816P-T01-393]	39 kOhm [CR0201-FW-3902GLF]	39 nF [C0402C393K4RACT U]
39 kOhm [4606X-102-393LF]	39 kOhm [4816P-T01-393LF]	39 kOhm [CR0402-FX-3902GLF]	
39 kOhm [4607X-101-393LF]	39 kOhm [4816P-T02-393]	39 kOhm [CR0603-FX-3902ELF]	

Multisim 14.1 Base Edition Components

39 nF [C0402C393K8RACT U]	39 nF [C0805C393K8RACT U]	39 nF [C1210C393K2RACT U]	39 nF [MDC10393K100A5 2P3TUBE]
39 nF [C0402C393K9RACT U]	39 nF [C0805F393K1RACT U]	39 nF [C1210C393K5RACT U]	39 nF [MDC10393K250A5 2P3TUBE]
39 nF [C0603C393K1RACT U]	39 nF [C0805F393K3RACT U]	39 nF [C1210C393KARACT U]	39 nF [MDC10393K400A5 2P3TUBE]
39 nF [C0603C393K3RACT U]	39 nF [C0805F393K4RACT U]	39 nF [C1812C393K1RACT U]	39 nF [MDC10393K50A52 P3TUBE]
39 nF [C0603C393K4RACT U]	39 nF [C0805F393K5RACT U]	39 nF [C1812C393K5RACT U]	39 nF [MDC10393K630A5 2P3TUBE]
39 nF [C0603C393K5RACT U]	39 nF [C1206C393K1RACT U]	39 nF [C2220C393K2GACT U]	39 nF [MDC15393K100B5 3P3TUBE]
39 nF [C0603C393K8RACT U]	39 nF [C1206C393K4RACT U]	39 nF [GMC5.7392K250J3 1TR12]	39 nF [MDC15393K250B5 3P3TUBE]
39 nF [C0805C393K1RACT U]	39 nF [C1206C393K5RACT U]	39 nF [GMC5.7393K50J31 TR12]	39 nF [MDC15393K400B5 3P3TUBE]
39 nF [C0805C393K3RACT U]	39 nF [C1206C393KARACT U]	39 nF [GMC7.3392K250K3 1TR12]	39 nF [MDC15393K50B53 P3TUBE]
39 nF [C0805C393K4RACT U]	39 nF [C1206C393M1UAC TU]	39 nF [GMC7.3392K63K31 TR12]	39 nF [MDC15393K630B5 3P3TUBE]
39 nF [C0805C393K5RACT U]	39 nF [C1210C393K1RACT U]	39 nF [GMC7.3393K63K31 TR12]	39 nF [MDK15393K100B5 3P3TUBE]

Multisim 14.1 Base Edition Components

39 nF [MDK15393K400B5 3P3TUBE]	39 Ohm [4306R- 101-390]	39 Ohm [4416P-1- 390]	39 Ohm [4611M- 101-390LF]
39 nF [MDK15393K50B53 P3TUBE]	39 Ohm [4306R- 101-390LF]	39 Ohm [4416P-1- 390LF]	39 Ohm [4612X- 102-390LF]
39 nF [MDS15393K400B5 3P3TUBE]	39 Ohm [4306R- 102-390]	39 Ohm [4416P- T01-390]	39 Ohm [4614X- 102-390LF]
39 nF [MDS15393K50B53 P3TUBE]	39 Ohm [4306R- 102-390LF]	39 Ohm [4420P-1- 390]	39 Ohm [4814P-1- 390]
39 nF [MDS15393K630B5 3P3TUBE]	39 Ohm [4308H- 102-390]	39 Ohm [4420P-1- 390LF]	39 Ohm [4814P-1- 390LF]
39 nF [MDS15393K630B5 3P3TUBE]	39 Ohm [4308H- 102-390LF]	39 Ohm [4420P- T01-390]	39 Ohm [4814P- T01-390]
39 Ohm [4114R-1- 390]	39 Ohm [4308R- 101-390]	39 Ohm [4604M- 101-390LF]	39 Ohm [4814P- T01-390LF]
39 Ohm [4114R-1- 390LF]	39 Ohm [4308R- 101-390LF]	39 Ohm [4606M- 101-390LF]	39 Ohm [4814P- T02-390]
39 Ohm [4114R-2- 390]	39 Ohm [4308R- 102-390]	39 Ohm [4606X- 101-390LF]	39 Ohm [4816P-1- 390]
39 Ohm [4114R-2- 390LF]	39 Ohm [4308R- 102-390LF]	39 Ohm [4606X- 102-390LF]	39 Ohm [4816P-1- 390LF]
39 Ohm [4116R-1- 390]	39 Ohm [4310R- 101-390]	39 Ohm [4608X- 101-390LF]	39 Ohm [4816P-2- 390]
39 Ohm [4116R-1- 390LF]	39 Ohm [4310R- 101-390LF]	39 Ohm [4608X- 102-390LF]	39 Ohm [4816P-2- 390LF]
39 Ohm [4116R-2- 390]	39 Ohm [4310R- 102-390]	39 Ohm [4609X- 101-390LF]	39 Ohm [4816P- T01-390]
39 Ohm [4116R-2- 390LF]	39 Ohm [4310R- 102-390LF]	39 Ohm [4610X- 101-390LF]	39 Ohm [4816P- T01-390LF]
39 Ohm [4116R-2- 390LF]	39 Ohm [4311R- 101-390]	39 Ohm [4610X- 102-390LF]	39 Ohm [4816P- T02-390]

Multisim 14.1 Base Edition Components

39 Ohm [4816P-T02-390LF]	39 Ohm [CR0201-JW-390GLF]	39 Ohm [CRT0603-DY-39R0ELF]	39 pF [C0805C390K1GACTU]
39 Ohm [4820P-1-390]	39 Ohm [CR0402-FX-39R0GLF]	39 Ohm [PWR163S-25-39R0J]	39 pF [C0805C390K2GACTU]
39 Ohm [4820P-T01-390]	39 Ohm [CR0402-JW-390GLF]	39 Ohm [PWR220T-20-39R0F]	39 pF [C0805C390K5GACTU]
39 Ohm [CAT10-390J4LF]	39 Ohm [CR0603-FX-39R0ELF]	39 Ohm [PWR220T-20-39R0J]	39 pF [C0805C390KBGAC TU]
39 Ohm [CAT16-390J2LF]	39 Ohm [CR0603-JW-390ELF]	39 Ohm [PWR4318W39R0JE]	39 pF [C0805C390KCGACTU]
39 Ohm [CAT16-390J4LF]	39 Ohm [CR0603-JW-390GLF]	39 pF [C0201C390K3GACTU]	39 pF [C1206C390K1GACTU]
39 Ohm [CAT16-39R0F4LF]	39 Ohm [CR0805-FX-39R0ELF]	39 pF [C0402C390K4GACTU]	39 pF [C1206C390K2GACTU]
39 Ohm [CAT25-390JALF]	39 Ohm [CR0805-FX-39R0GLF]	39 pF [C0402C390K5GACTU]	39 pF [C1206C390K5GACTU]
39 Ohm [CAY10-390J2LF]	39 Ohm [CR0805-JW-390ELF]	39 pF [C0402C390K8GACTU]	39 pF [C1206C390KBGAC TU]
39 Ohm [CAY10-390J4LF]	39 Ohm [CR0805-JW-390GLF]	39 pF [C0603C390K2GACTU]	39 pF [C1210C390KBGAC TU]
39 Ohm [CAY16-390J4LF]	39 Ohm [CR1206-FX-39R0ELF]	39 pF [C0603C390K5GACTU]	39 pF [C1812C390KBGAC TU]
39 Ohm [CAY16-390J8LF]	39 Ohm [CR1206-JW-390ELF]		
39 Ohm [CAY16-39R0F4LF]	39 Ohm [CR1206-JW-390GLF]		
39 Ohm [CAY17-390JALF]	39 Ohm [CR2010-JW-390ELF]		
39 Ohm [CR0201-FW-39R0GLF]	39 Ohm [CR2512-JW-390ELF]		

Multisim 14.1 Base Edition Components

39 pF [C1825C390KBGAC TU]	39 uH [SDR0703- 390KL]	39 uH [SRR0908- 390ML]	39 uH [SRR5028- 390Y]
39 pF [C2220C390KBGAC TU]	39 uH [SDR0805- 390KL]	39 uH [SRR1003- 390M]	39 uH [SRR6028- 390Y]
39 pF [C2225C390KBGAC TU]	39 uH [SDR0906- 390KL]	39 uH [SRR1005- 390Y]	39 uH [SRR6038- 390Y]
39 pF [CA064C390K5GAC TU]	39 uH [SDR1105- 390KL]	39 uH [SRR1205- 390ML]	39 uH [SRR6040A- 390M]
39 uF [16SVPC39MV]	39 uH [SDR1307- 390KL]	39 uH [SRR1206- 390YL]	39 uH [SRR7045- 390M]
39 uH [SDE0403A- 390K]	39 uH [SDR1307A- 390K]	39 uH [SRR1208- 390YL]	39.2 kOhm [CAY16- 3922F4LF]
39 uH [SDE0604A- 390M]	39 uH [SRP1770TA- 390M]	39 uH [SRR1210- 390M]	39.2 kOhm [CR0402-FX- 3922GLF]
39 uH [SDE0805A- 390M]	39 uH [SRP6540- 390M]	39 uH [SRR1210A- 390M]	39.2 kOhm [CR0603-FX- 3922ELF]
39 uH [SDE1006A- 390M]	39 uH [SRR0735A- 390M]	39 uH [SRR1240- 390M]	39.2 kOhm [CR0805-FX- 3922ELF]
39 uH [SDR0302- 390KL]	39 uH [SRR0745A- 390M]	39 uH [SRR1260- 390M]	39.2 kOhm [CR1206-FX- 3922ELF]
39 uH [SDR0403- 390KL]	39 uH [SRR0804- 390Y]	39 uH [SRR1260A- 390M]	39.2 Ohm [CAY16- 39R2F4LF]
39 uH [SDR0503- 390KL]	39 uH [SRR0805- 390Y]	39 uH [SRR4018- 390Y]	39.2 Ohm [CR0402- FX-39R2GLF]
39 uH [SDR0603- 390KL]	39 uH [SRR0905- 390Y]	39 uH [SRR4028- 390Y]	39.2 Ohm [CR0603- FX-39R2ELF]
39 uH [SDR0604- 390KL]	39 uH [SRR0906- 390ML]	39 uH [SRR5018- 390Y]	39.2 Ohm [CR0603- FX-39R2GLF]

Multisim 14.1 Base Edition Components

39.2 Ohm [CR0805-FX-39R2ELF]	390 kOhm [4308R-102-394LF]	390 kOhm [4610X-102-394LF]	390 kOhm [CR0603-FX-3903ELF]
39.2 Ohm [CR0805-FX-39R2GLF]	390 kOhm [4310M-101-394]	390 kOhm [4814P-1-394]	390 kOhm [CR0603-JW-394ELF]
39.2 Ohm [CR1206-FX-39R2ELF]	390 kOhm [4310M-101-394LF]	390 kOhm [4814P-1-394LF]	390 kOhm [CR0603-JW-394GLF]
39.2 Ohm [CR2512-FX-39R2ELF]	390 kOhm [4310R-101-394]	390 kOhm [4816P-1-394]	390 kOhm [CR0805-FX-3903ELF]
39.2 Ohm [CRM1206-FX-39R2ELF]	390 kOhm [4310R-101-394LF]	390 kOhm [4816P-1-394LF]	390 kOhm [CR0805-JW-394ELF]
39.2 Ohm [CRM2512-FX-39R2ELF]	390 kOhm [4310R-102-394]	390 kOhm [4816P-T01-394]	390 kOhm [CR1206-FX-3903ELF]
390 kOhm [4116R-1-394]	390 kOhm [4604X-102-394LF]	390 kOhm [4816P-T02-394]	390 kOhm [CR1206-JW-394ELF]
390 kOhm [4116R-1-394LF]	390 kOhm [4605X-101-394LF]	390 kOhm [4816P-T02-394LF]	390 kOhm [CR1206-JW-394GLF]
390 kOhm [4116R-2-394]	390 kOhm [4606X-101-394LF]	390 kOhm [CAT16-394J4LF]	390 mOhm [CRL0603-FW-R390ELF]
390 kOhm [4306R-101-394]	390 kOhm [4606X-102-394LF]	390 kOhm [CAT25-394JALF]	390 mOhm [CRL0603-JW-R390ELF]
390 kOhm [4306R-101-394LF]	390 kOhm [4608X-101-394LF]	390 kOhm [CAY16-394J4LF]	390 mOhm [CRL0805-FW-R390ELF]
390 kOhm [4306R-102-394]	390 kOhm [4608X-102-394LF]	390 kOhm [CAY16-394J8LF]	
390 kOhm [4308R-101-394]	390 kOhm [4609M-101-394LF]	390 kOhm [CHV0805-FX-3903ELF]	
390 kOhm [4308R-101-394LF]	390 kOhm [4610X-101-394LF]	390 kOhm [CR0402-FX-3903GLF]	
390 kOhm [4308R-102-394]			

Multisim 14.1 Base Edition Components

390 mOhm [CRL0805-JW- R390ELF]	390 nF [C0603C394K8PACT U]	390 nF [C1206C394K8RACT U]	390 nF [C1812C394M5UAC TU]
390 mOhm [CRL1206-FW- R390ELF]	390 nF [C0603C394K8RACT U]	390 nF [C1206F394K3RACT U]	390 nF [C1812F394K1RACT U]
390 mOhm [CRL1206-JW- R390ELF]	390 nF [C0603C394K9RACT U]	390 nF [C1206F394K4RACT U]	390 nF [C1812F394K2RACT U]
390 mOhm [CRL2010-FW- R390ELF]	390 nF [C0805C394K3RACT U]	390 nF [C1210C394K3RACT U]	390 nF [C1812F394K3RACT U]
390 mOhm [CRL2010-JW- R390ELF]	390 nF [C0805C394K4RACT U]	390 nF [C1210C394K5RACT U]	390 nF [C1812F394K5RACT U]
390 mOhm [CRL2512-FW- R390ELF]	390 nF [C0805C394K8RACT U]	390 nF [C1210F394K3RACT U]	390 nF [C1825C394K1RACT U]
390 mOhm [CRL2512-JW- R390ELF]	390 nF [C0805C394K9RACT U]	390 nF [C1210F394K4RACT U]	390 nF [C1825C394K2RACT U]
390 mOhm [CRM2010-FX- R390ELF]	390 nF [C1206C394K1RACT U]	390 nF [C1210F394K5RACT U]	390 nF [C1825C394K5RACT U]
390 mOhm [CRM2512-FX- R390ELF]	390 nF [C1206C394K3RACT U]	390 nF [C1812C394K1RACT U]	390 nF [C2225C394K1RACT U]
390 nF [C0603C394K4PACT U]	390 nF [C1206C394K4RACT U]	390 nF [C1812C394K5RACT U]	390 nF [C2225C394K2RACT U]
390 nF [C0603C394K4RACT U]	390 nF [C1206C394K5RACT U]	390 nF [C1812C394KARACT U]	390 nF [GMC7.3394K63K37 TR12]

Multisim 14.1 Base Edition Components

390 nF [MDC10394K100A5 2P3TUBE]	390 nF [MMC12.7394K250 B31TR24]	390 Ohm [4306H- 101-391LF]	390 Ohm [4310H- 101-391]
390 nF [MDC10394K250A5 2P3TUBE]	390 nF [MMC7.3394K50K3 5TR12]	390 Ohm [4306M- 101-391]	390 Ohm [4310H- 101-391LF]
390 nF [MDC10394K400A5 8P7TUBE]	390 nF [MMC7.3394K63K3 5TR12]	390 Ohm [4306M- 101-391LF]	390 Ohm [4310M- 101-391]
390 nF [MDC10394K400A5 8P8TUBE]	390 nH [SRP1038A- R39M]	390 Ohm [4306R- 101-391LF]	390 Ohm [4310M- 101-391LF]
390 nF [MDC10394K50A52 P3TUBE]	390 nH [SRP1040- R39M]	390 Ohm [4306R- 102-391]	390 Ohm [4310R- 101-391]
390 nF [MDC15394K100B5 3P3TUBE]	390 Ohm [4114R-1- 391]	390 Ohm [4306R- 102-391LF]	390 Ohm [4310R- 102-391]
390 nF [MDC15394K250B5 3P3TUBE]	390 Ohm [4114R-1- 391LF]	390 Ohm [4308H- 102-391]	390 Ohm [4310R- 102-391LF]
390 nF [MDC15394K50B53 P3TUBE]	390 Ohm [4114R-2- 391]	390 Ohm [4308M- 102-391]	390 Ohm [4311R- 101-391]
390 nF [MDK15394K100B5 3P3TUBE]	390 Ohm [4114R-2- 391LF]	390 Ohm [4308R- 101-391]	390 Ohm [4311R- 101-391LF]
390 nF [MDK15394K50B53 P3TUBE]	390 Ohm [4116R-1- 391]	390 Ohm [4308R- 101-391LF]	390 Ohm [4416P-2- 391]
390 nF [MDK15394K100B5 3P3TUBE]	390 Ohm [4116R-1- 391LF]	390 Ohm [4308R- 102-391]	390 Ohm [4416P- T01-391]
390 nF [MDK15394K50B53 P3TUBE]	390 Ohm [4116R-2- 391]	390 Ohm [4308R- 102-391LF]	390 Ohm [4416P- T02-391]
390 nF [MDS15394K50B53 P3TUBE]	390 Ohm [4116R-2- 391LF]	390 Ohm [4309R- 101-391]	390 Ohm [4420P-1- 391]
	390 Ohm [4306H- 101-391]	390 Ohm [4309R- 101-391LF]	390 Ohm [4420P- T01-391]

Multisim 14.1 Base Edition Components

390 Ohm [4420P-T02-391]	390 Ohm [4610X-101-391LF]	390 Ohm [4816P-T02-391]	390 Ohm [CR0603-JW-391ELF]
390 Ohm [4604X-102-391LF]	390 Ohm [4610X-102-391LF]	390 Ohm [4816P-T02-391LF]	390 Ohm [CR0805-FX-3900ELF]
390 Ohm [4605X-101-391LF]	390 Ohm [4610X-AP2-391LF]	390 Ohm [4820P-2-391]	390 Ohm [CR0805-FX-3900GLF]
390 Ohm [4606X-101-391LF]	390 Ohm [4614X-102-391LF]	390 Ohm [4820P-T01-391]	390 Ohm [CR0805-JW-391ELF]
390 Ohm [4606X-102-391LF]	390 Ohm [4814P-2-391]	390 Ohm [4820P-T02-391]	390 Ohm [CR1206-FX-3900ELF]
390 Ohm [4606X-AP1-391LF]	390 Ohm [4814P-2-391LF]	390 Ohm [CAT16-391J4LF]	390 Ohm [CR1206-JW-391ELF]
390 Ohm [4606X-AP2-391LF]	390 Ohm [4814P-T01-391]	390 Ohm [CAT25-391JALF]	390 Ohm [CR1206-JW-391GLF]
390 Ohm [4607X-101-391LF]	390 Ohm [4814P-T02-391]	390 Ohm [CAY10-391J4LF]	390 Ohm [CR2010-JW-391ELF]
390 Ohm [4608H-101-391LF]	390 Ohm [4814P-T02-391LF]	390 Ohm [CAY16-3900F4LF]	390 Ohm [CR2512-JW-391ELF]
390 Ohm [4608M-102-391LF]	390 Ohm [4816P-1-391]	390 Ohm [CAY16-391J4LF]	390 Ohm [CRM2512-FX-3900ELF]
390 Ohm [4608X-101-391LF]	390 Ohm [4816P-1-391LF]	390 Ohm [CAY16-391J8LF]	390 Ohm [PWR263S-35-3900FE]
390 Ohm [4608X-102-391LF]	390 Ohm [4816P-2-391]	390 Ohm [CR0402-FX-3900GLF]	390 Ohm [PWR4318W3900FE]
390 Ohm [4608X-AP2-391LF]	390 Ohm [4816P-2-391LF]	390 Ohm [CR0402-JW-391GLF]]
390 Ohm [4609X-101-391LF]	390 Ohm [4816P-T01-391]	390 Ohm [CR0603-FX-3900ELF]	390 Ohm [PWR4318W3900JE]
390 Ohm [4610M-101-391LF]	390 Ohm [4816P-T01-391LF]	390 Ohm [CR0603-FX-3900GLF]]

Multisim 14.1 Base Edition Components

390 Ohm [PWR4525W3900JE]	390 pF [C0603C391K3RACT U]	390 pF [C1206C391K2GACT U]	390 uF [6SVPC390M] 390 uF [A700X397M002AT E010] 390 uF [A700X397M002AT E015] 390 uF [EEFCX0D391R] 390 uF [EEFCX0E391R] 390 uF [EEFSX0D391E4] 390 uF [EEFSX0D391ER] 390 uF [EEFSX0D391XE] 390 uF [EEFSX0E391E4] 390 uF [EEFSX0E391ER] 390 uF [EEFSX0E391XE] 390 uH [SDE0805A- 391K] 390 uH [SDE1006A- 391K] 390 uH [SDR0302- 391KL] 390 uH [SDR0403- 391KL]
390 Ohm [PWR5322W3900JE]	390 pF [C0603C391K4RACT U]	390 pF [C1206C391K5GACT U]	
390 pF [C0402C391K1HACT U]	390 pF [C0603C391K5GACT U]	390 pF [C1206C391KBGAC TU]	
390 pF [C0402C391K3HACT U]	390 pF [C0603C391K5RACT U]	390 pF [C1206C391KCGAC TU]	
390 pF [C0402C391K3RACT U]	390 pF [C0805C391K1GACT U]	390 pF [C1210C391KBGAC TU]	
390 pF [C0402C391K4RACT U]	390 pF [C0805C391K1RACT U]	390 pF [C1812C391KBGAC TU]	
390 pF [C0402C391K5HACT U]	390 pF [C0805C391K2GACT U]	390 pF [C1825C391KBGAC TU]	
390 pF [C0402C391K5RACT U]	390 pF [C0805C391K4RACT U]	390 pF [C2220C391KBGAC TU]	
390 pF [C0603C391K1RACT U]	390 pF [C0805C391K5GACT U]	390 pF [C2225C391KBGAC TU]	
390 pF [C0603C391K2RACT U]	390 pF [C0805C391K5RACT U]	390 pF [CA064C391K5GAC TU]	
390 pF [C0603C391K3GACT U]	390 pF [C1206C391K1GACT U]	390 uF [2R5SVPC390MV] 390 uF [2SEPC390M]	

Multisim 14.1 Base Edition Components

390 uH [SDR0503-391KL]	390 uH [SRR1003-391Y]	392 kOhm [CR0603-FX-3923ELF]	3KASMC24AHE3/9A T
390 uH [SDR0603-391KL]	390 uH [SRR1005-391K]	392 kOhm [CR0805-FX-3923ELF]	3KASMC28AHM3/5 7T
390 uH [SDR0604-391KL]	390 uH [SRR1205-391KL]	392 kOhm [CR1206-FX-3923ELF]	3Line_Bussed
390 uH [SDR0703-391KL]	390 uH [SRR1206-391KL]	392 Ohm [4816P-1-3920F]	3Line_Isolated
390 uH [SDR0805-391KL]	390 uH [SRR1208-391KL]	392 Ohm [CR0402-FX-3920GLF]	3LN01C-TB-E
390 uH [SDR0906-391KL]	390 uH [SRR1210-391M]	392 Ohm [CR0603-FX-3920ELF]	3LN01C-TB-H
390 uH [SDR1006-391KL]	390 uH [SRR1210A-391M]	392 Ohm [CR0805-FX-3920ELF]	3LN01M-TL-E
390 uH [SDR1307-391KL]	390 uH [SRR1240-391K]	392 Ohm [CR1206-FX-3920ELF]	3LN01M-TL-H
390 uH [SDR1307A-391K]	390 uH [SRR1260-391K]	392 Ohm [CRM1206-FX-3920ELF]	3LN01SS-TL-E
390 uH [SRR0735A-391M]	390 uH [SRR1260A-391K]	392 Ohm [CRT1206-BY-3920ELF]	3LN01S-TL-E
390 uH [SRR0745A-391M]	390 uH [SRR1280-391K]	3BH41	3LP01C-TB-E
390 uH [SRR0804-391K]	390 uH [SRR4028-391Y]	3GH41	3LP01C-TB-H
390 uH [SRR0905-391K]	390 uH [SRR7045-391M]	3JH41	3LP01M-TL-E
390 uH [SRR0906-391YL]	392 kOhm [CR0201-FW-3923GLF]	3KASMC15AHE3/57 T	3LP01M-TL-H
390 uH [SRR0908-391YL]	392 kOhm [CR0402-FX-3923GLF]	3KASMC17AHM3_A /H	3LP01SS-TL-E
			3LP01SS-TL-H
			3LP01S-TL-E
			3N246
			3N247
			3N248
			3N249
			3N250
			3N251

Multisim 14.1 Base Edition Components

3N252	4 Ohm [PWR163S-25-4R00FE]	4.02 MOhm [CR1206-FW-4024ELF]	4.22 kOhm [CR1206-FX-4221ELF]
3N253	4 Ohm [PWR163S-25-4R00JE]	4.1 uH [SRR5018-4R1Y]	4.22 kOhm [CR2010-FX-4221ELF]
3N254	4 Ohm [PWR220T-35-4R00F]	4.12 kOhm [CAY16-4121F4LF]	4.3 kOhm [4308R-102-432]
3N255	4 Ohm [PWR221T-30-4R00F]	4.12 kOhm [CR0402-FX-4121GLF]	4.3 kOhm [CAY10-432J4LF]
3N256	4 Ohm [PWR263S-35-4R00F]	4.12 kOhm [CR0603-FX-4121ELF]	4.3 kOhm [CAY16-432J4LF]
3N257	4.02 kOhm [CR0402-FX-4021GLF]	4.12 kOhm [CR0805-FX-4121ELF]	4.3 kOhm [CR0402-FX-4301GLF]
3N258	4.02 kOhm [CR0603-FX-4021ELF]	4.12 kOhm [CR1206-FX-4121ELF]	4.3 kOhm [CR0603-FX-4301ELF]
3N259	4.02 kOhm [CR0805-FX-4021ELF]	4.2 uH [SRP1205-4R0Y]	4.3 kOhm [CR0603-JW-432ELF]
3PDT_DB	4.02 kOhm [CRA2512-FZ-R004ELF]	4.2 uH [SRR5028-4R2Y]	4.3 kOhm [CR0805-FX-4301ELF]
3PDT_SB	4.02 kOhm [CRT0402-FZ-4021GLF]	4.22 kOhm [CR0402-FX-4221GLF]	4.3 kOhm [CR0805-JW-432ELF]
3PST_DB	4.02 kOhm [CRT0603-BY-4021ELF]	4.22 kOhm [CR0603-FX-4221ELF]	4.3 kOhm [CR1206-FX-4301ELF]
3PST_SB	4.02 kOhm [CRT0805-BY-4021ELF]	4.22 kOhm [PWR163S-25-4301FE]	
4 kOhm [4116R-1-402]			
4 kOhm [4116R-1-402LF]			
4 kOhm [CR1206-FX-4001ELF]			
4 mOhm [CRA2512-FZ-R004ELF]			
4 mOhm [CRE2512-FZ-R004E-2]			
4 mOhm [CRE2512-FZ-R004E-3]			
4 mOhm [CRF2512-FX-R004ELF]			

Multisim 14.1 Base Edition Components

4.3 MOhm [4308R-102-435]	4.3 nF [C1825C432KBGAC TU]	4.3 Ohm [CRL2010-FW-4R30ELF]	4.42 kOhm [CR0603-FX-4421ELF]
4.3 MOhm [CR0603-JW-435ELF]	4.3 nF [C2220C432KBGAC TU]	4.3 Ohm [CRL2010-JW-4R30ELF]	4.42 kOhm [CR0805-FX-4421ELF]
4.3 MOhm [CR0805-JW-435ELF]	4.3 nF [C2225C432KBGAC TU]	4.3 Ohm [CRL2512-FW-4R30ELF]	4.42 kOhm [CR1206-FX-4421ELF]
4.3 MOhm [CR1206-JW-435ELF]	4.3 Ohm [CR0402-J/-4R3GLF]	4.32 kOhm [CAY16-4321F4LF]	4.42 kOhm [CRT0603-BY-4421ELF]
4.3 nF [C0603C432K1HACT U]	4.3 Ohm [CR0603-J/-4R3ELF]	4.32 kOhm [CR0402-FX-4321GLF]	4.42 kOhm [CRT0805-BX-4421ELF]
4.3 nF [C0603C432K3HACT U]	4.3 Ohm [CR0603-J/-4R3GLF]	4.32 kOhm [CR0603-FX-4321ELF]	4.42 MOhm [CR1206-FW-4424ELF]
4.3 nF [C0603C432K5HACT U]	4.3 Ohm [CR0805-J/-4R3ELF]	4.32 kOhm [CR0805-FX-4321ELF]	4.5 Ohm [PWR220T-35-4R50F]
4.3 nF [C0805C432K1GACT U]	4.3 Ohm [CRL0603-FW-4R30ELF]	4.32 kOhm [CR0805-FX-4321GLF]	4.5 uH [SDR1045-4R5M]
4.3 nF [C0805C432K1HACT U]	4.3 Ohm [CRL0603-JW-4R30ELF]	4.32 kOhm [CR1206-FX-4321ELF]	4.5 uH [SRR1208-4R5ML]
4.3 nF [C0805C432K3HACT U]	4.3 Ohm [CRL0805-FW-4R30ELF]	4.4 uH [SRU2009-4R4Y]	4.53 kOhm [CAY16-4531F4LF]
4.3 nF [C0805C432K5HACT U]	4.3 Ohm [CRL1206-FW-4R30ELF]	4.42 kOhm [CR0402-FX-4421GLF]	4.53 kOhm [CR0201-FW-4531GLF]
	4.3 Ohm [CRL1206-JW-4R30ELF]		

Multisim 14.1 Base Edition Components

4.53 kOhm [CR0402-FX- 4531GLF]	4.64 kOhm [CR2512-FX- 4641ELF]	4.7 kOhm [4304M- 101-472]	4.7 kOhm [4308H- 102-472LF]
4.53 kOhm [CR0603-FX- 4531ELF]	4.64 kOhm [CRT0402-FZ- 4641GLF]	4.7 kOhm [4304M- 101-472LF]	4.7 kOhm [4308M- 101-472]
4.53 kOhm [CR0805-FX- 4531ELF]	4.64 kOhm [CRT0603-BY- 4641ELF]	4.7 kOhm [4306H- 101-472]	4.7 kOhm [4308M- 101-472LF]
4.53 kOhm [CR1206-FX- 4531ELF]	4.7 kOhm [4108R- 1-472]	4.7 kOhm [4306H- 102-472]	4.7 kOhm [4308M- 102-472LF]
4.53 kOhm [CRT0603-FX- 4531ELF]	4.7 kOhm [4108R- 1-472LF]	4.7 kOhm [4306M- 101-472]	4.7 kOhm [4308R- 101-472]
4.53 kOhm [CRT0805-BY- 4531ELF]	4.7 kOhm [4108R- 2-472LF]	4.7 kOhm [4306M- 101-472LF]	4.7 kOhm [4308R- 101-472LF]
4.6 uH [SDR1305- 4R6Y]	4.7 kOhm [4114R- 1-472]	4.7 kOhm [4306M- 102-472]	4.7 kOhm [4308R- 102-472]
4.64 kOhm [CR0402-FX- 4641GLF]	4.7 kOhm [4114R- 1-472LF]	4.7 kOhm [4306R- 101-472]	4.7 kOhm [4308R- 102-472LF]
4.64 kOhm [CR0603-FX- 4641ELF]	4.7 kOhm [4114R- 2-472]	4.7 kOhm [4306R- 101-472LF]	4.7 kOhm [4309R- 101-472]
4.64 kOhm [CR0805-FX- 4641ELF]	4.7 kOhm [4114R- 2-472LF]	4.7 kOhm [4306R- 102-472]	4.7 kOhm [4309R- 101-472LF]
4.64 kOhm [CR1206-FX- 4641ELF]	4.7 kOhm [4116R- 1-472]	4.7 kOhm [4306R- 102-472LF]	4.7 kOhm [4310H- 101-472]
	4.7 kOhm [4116R- 1-472LF]	4.7 kOhm [4308H- 101-472]	4.7 kOhm [4310H- 101-472LF]
	4.7 kOhm [4116R- 2-472]	4.7 kOhm [4308H- 101-472LF]	4.7 kOhm [4310H- 102-472]
	4.7 kOhm [4116R- 2-472LF]	4.7 kOhm [4308H- 102-472]	4.7 kOhm [4310H- 102-472LF]

Multisim 14.1 Base Edition Components

4.7 kOhm [4310M-101-472]	4.7 kOhm [4420P-1-472]	4.7 kOhm [4606H-101-472LF]	4.7 kOhm [4608X-AP2-472LF]
4.7 kOhm [4310M-101-472LF]	4.7 kOhm [4420P-1-472LF]	4.7 kOhm [4606H-102-472LF]	4.7 kOhm [4609H-101-472LF]
4.7 kOhm [4310R-101-472]	4.7 kOhm [4420P-2-472]	4.7 kOhm [4606M-101-472LF]	4.7 kOhm [4609M-101-472LF]
4.7 kOhm [4310R-101-472LF]	4.7 kOhm [4420P-2-472LF]	4.7 kOhm [4606X-101-472LF]	4.7 kOhm [4609X-101-472LF]
4.7 kOhm [4310R-102-472]	4.7 kOhm [4420P-T01-472]	4.7 kOhm [4606X-102-472LF]	4.7 kOhm [4609X-AP1-472LF]
4.7 kOhm [4310R-102-472LF]	4.7 kOhm [4420P-T01-472LF]	4.7 kOhm [4606X-AP1-472LF]	4.7 kOhm [4610H-101-472LF]
4.7 kOhm [4311R-101-472]	4.7 kOhm [4420P-T02-472]	4.7 kOhm [4606X-AP2-472LF]	4.7 kOhm [4610H-102-472LF]
4.7 kOhm [4311R-101-472LF]	4.7 kOhm [4420P-T02-472LF]	4.7 kOhm [4607X-101-472LF]	4.7 kOhm [4610M-101-472LF]
4.7 kOhm [4416P-1-472]	4.7 kOhm [4604H-101-472LF]	4.7 kOhm [4608H-101-472LF]	4.7 kOhm [4610M-102-472LF]
4.7 kOhm [4416P-1-472LF]	4.7 kOhm [4604X-101-472LF]	4.7 kOhm [4608H-102-472LF]	4.7 kOhm [4610X-101-472LF]
4.7 kOhm [4416P-2-472]	4.7 kOhm [4604X-102-472LF]	4.7 kOhm [4608M-101-472LF]	4.7 kOhm [4610X-102-472LF]
4.7 kOhm [4416P-2-472LF]	4.7 kOhm [4605H-101-472LF]	4.7 kOhm [4608M-102-472LF]	4.7 kOhm [4610X-AP1-472LF]
4.7 kOhm [4416P-T01-472]	4.7 kOhm [4605M-101-472LF]	4.7 kOhm [4608X-101-472LF]	4.7 kOhm [4610X-AP2-472LF]
4.7 kOhm [4416P-T02-472]	4.7 kOhm [4605X-101-472LF]	4.7 kOhm [4608X-102-472LF]	4.7 kOhm [4611X-101-472LF]
4.7 kOhm [4416P-T02-472LF]	4.7 kOhm [4605X-AP1-472LF]	4.7 kOhm [4608X-AP1-472LF]	4.7 kOhm [4612X-101-472LF]

Multisim 14.1 Base Edition Components

4.7 kOhm [4612X-102-472LF]	4.7 kOhm [4816P-2-472]	4.7 kOhm [4820P-2-472LF]	4.7 kOhm [CAY16-472J4GLF]
4.7 kOhm [4613X-101-472LF]	4.7 kOhm [4816P-2-472F]	4.7 kOhm [4820P-T01-472]	4.7 kOhm [CAY16-472J4LF]
4.7 kOhm [4614X-101-472LF]	4.7 kOhm [4816P-2-472LF]	4.7 kOhm [4820P-T01-472LF]	4.7 kOhm [CAY16-472J8LF]
4.7 kOhm [4614X-102-472LF]	4.7 kOhm [4816P-T01-472]	4.7 kOhm [4820P-T02-472]	4.7 kOhm [CAY17-472JALF]
4.7 kOhm [4814P-1-472]	4.7 kOhm [4816P-T01-472LF]	4.7 kOhm [4820P-T02-472LF]	4.7 kOhm [CR0201-FW-4701GLF]
4.7 kOhm [4814P-1-472LF]	4.7 kOhm [4816P-T02-472]	4.7 kOhm [CAT10-472J4LF]	4.7 kOhm [CR0201-JW-472GLF]
4.7 kOhm [4814P-2-472]	4.7 kOhm [4816P-T02-472LF]	4.7 kOhm [CAT16-4701F4LF]	4.7 kOhm [CR0402-FX-4701GLF]
4.7 kOhm [4814P-2-472LF]	4.7 kOhm [4818P-2-472]	4.7 kOhm [CAT16-472J2LF]	4.7 kOhm [CR0402-JW-472GLF]
4.7 kOhm [4814P-T01-472]	4.7 kOhm [4818P-2-472LF]	4.7 kOhm [CAT16-472J4LF]	4.7 kOhm [CR0603-FX-4701ELF]
4.7 kOhm [4814P-T01-472LF]	4.7 kOhm [4818P-T02-472]	4.7 kOhm [CAT16-472J8LF]	4.7 kOhm [CR0603-JW-472ELF]
4.7 kOhm [4814P-T02-472]	4.7 kOhm [4820P-1-472]	4.7 kOhm [CAT25-472JALF]	4.7 kOhm [CR0603-JW-472GLF]
4.7 kOhm [4814P-T02-472LF]	4.7 kOhm [4820P-1-472F]	4.7 kOhm [CAY10-472J2LF]	4.7 kOhm [CR0805-FX-4701ELF]
4.7 kOhm [4816P-1-472]	4.7 kOhm [4820P-1-472LF]	4.7 kOhm [CAY10-472J4LF]	4.7 kOhm [CR0805-FX-4701GLF]
4.7 kOhm [4816P-1-472F]	4.7 kOhm [4820P-2-472]	4.7 kOhm [CAY16-4701F4LF]	4.7 kOhm [CR0805-JW-472ELF]
4.7 kOhm [4816P-1-472LF]	4.7 kOhm [4820P-2-472F]	4.7 kOhm [CAY16-472J2LF]	4.7 kOhm [CR0805-JW-472GLF]

Multisim 14.1 Base Edition Components

4.7 kOhm [CR1206-FX-4701ELF]	4.7 kOhm [PWR4525W4701J]	4.7 MOhm [4310R-101-475LF]	4.7 MOhm [CR1206-FW-4704ELF]
4.7 kOhm [CR1206-JW-472ELF]	4.7 kOhm [PWR4525W4701JE]	4.7 MOhm [4604X-102-475LF]	4.7 MOhm [CR1206-JW-475ELF]
4.7 kOhm [CR1206-JW-472GLF]	4.7 kOhm [PWR6327W4701J]	4.7 MOhm [4608X-102-475LF]	4.7 nF [03063C472KAT2A]
4.7 kOhm [CR2512-JW-472ELF]	4.7 kOhm [PWR6327W4701JE]	4.7 MOhm [CAT25-475JALF]	4.7 nF [03066C472KAT2A]
4.7 kOhm [CRM1206-JW-472ELF]	4.7 mH [SDR0503-472JL]	4.7 MOhm [CAY16-4704F4LF]	4.7 nF [0306YC472KAT2A]
4.7 kOhm [CRM2010-JW-472ELF]	4.7 mH [SDR0805-472KL]	4.7 MOhm [CHV0603-JW-475ELF]	4.7 nF [0306ZC472KAT2A]
4.7 kOhm [CRM2512-FX-4701ELF]	4.7 mH [SDR0906-472KL]	4.7 MOhm [CHV2010-JW-475ELF]	4.7 nF [05085C472KAT2V]
4.7 kOhm [CRS1206-FX-4701ELF]	4.7 mH [SDR1005-472KL]	4.7 MOhm [CR0402-FX-4704GLF]	4.7 nF [06123C472KAT2S]
4.7 kOhm [CRS2010-FX-4701ELF]	4.7 mH [SDR1006-472KL]	4.7 MOhm [CR0402-JW-475GLF]	4.7 nF [C0402C472K3RACTU]
4.7 kOhm [CRT0402-FZ-4701GLF]	4.7 mH [SRR0906-472YL]	4.7 MOhm [CR0603-JW-475ELF]	4.7 nF [C0402C472K4RACTU]
4.7 kOhm [CRT0603-FX-4701ELF]	4.7 mH [SRR0908-472YL]	4.7 MOhm [CR0805-FX-4704ELF]	4.7 nF [C0402C472K5RACTU]
4.7 kOhm [CRT0805-BY-4701ELF]	4.7 mH [SRR1208-472KL]	4.7 MOhm [CR0805-JW-475ELF]	4.7 nF [C0402C472K8RACTU]
	4.7 MOhm [4310R-101-475]		4.7 nF [C0402C472K9RACTU]

Multisim 14.1 Base Edition Components

4.7 nF [C0603C472K1HACT U]	4.7 nF [C0805C472K1HACT U]	4.7 nF [C1206C472K2RACT U]	4.7 nF [C1812C472K2GACT U]
4.7 nF [C0603C472K1RACT U]	4.7 nF [C0805C472K1RACT U]	4.7 nF [C1206C472K3RACT U]	4.7 nF [C1812C472K5GACT U]
4.7 nF [C0603C472K3GACT U]	4.7 nF [C0805C472K2RACT U]	4.7 nF [C1206C472K4GACT U]	4.7 nF [C1825C472K2GACT U]
4.7 nF [C0603C472K3HACT U]	4.7 nF [C0805C472K3GACT U]	4.7 nF [C1206C472K5GACT U]	4.7 nF [C1825C472KBGAC TU]
4.7 nF [C0603C472K3RACT U]	4.7 nF [C0805C472K3HACT U]	4.7 nF [C1206C472K5RACT U]	4.7 nF [C2220C472KBGAC TU]
4.7 nF [C0603C472K4RACT U]	4.7 nF [C0805C472K3RACT U]	4.7 nF [C1210C472K1GACT U]	4.7 nF [C2225C472K2GACT U]
4.7 nF [C0603C472K5HACT U]	4.7 nF [C0805C472K4RACT U]	4.7 nF [C1210C472K1RACT U]	4.7 nF [C2225C472KBGAC TU]
4.7 nF [C0603C472K5RACT U]	4.7 nF [C0805C472K5HACT U]	4.7 nF [C1210C472K2RACT U]	4.7 nF [CA064C472K3RACT U]
4.7 nF [C0603C472K8RACT U]	4.7 nF [C0805C472K5RACT U]	4.7 nF [C1210C472K5GACT U]	4.7 nF [CA064C472K5RACT U]
4.7 nF [C0603C472K9RACT U]	4.7 nF [C0805C472KARACT U]	4.7 nF [C1210C472K5RACT U]	4.7 nF [GMC5.7472K100J3 1TR12]
4.7 nF [C0805C472K1GACT U]	4.7 nF [C1206C472K1RACT U]	4.7 nF [C1812C472K1GACT U]	4.7 nF [GMC5.7472K50J31 TR12]

Multisim 14.1 Base Edition Components

4.7 Ohm [FW20A4R70JA]	4.7 Ohm [PWR220T-35-4R70J]	4.7 Ohm [PWR263S-35-4R70J]	4.7 uF [C0805C475K8PACT U]
4.7 Ohm [FW30A4R70JA]	4.7 Ohm [PWR221T-30-4R70F]	4.7 Ohm [PWR3014WA4R70J E]	4.7 uF [C0805C475K9PACT U]
4.7 Ohm [FW50A4R70JA]	4.7 Ohm [PWR221T-30-4R70J]	4.7 Ohm [PWR4318W4R70J E]	4.7 uF [C1206C475K3PACT U]
4.7 Ohm [PWR163S-25-4R70F]	4.7 Ohm [PWR2615W4R70F]	4.7 Ohm [PWR5322W4R70J]	4.7 uF [C1206C475K3RACT U]
4.7 Ohm [PWR163S-25-4R70J]	4.7 Ohm [PWR2615W4R70F E]	4.7 Ohm [PWR5322W4R70J E]	4.7 uF [C1206C475K4PACT U]
4.7 Ohm [PWR163S-25-4R70JE]	4.7 Ohm [PWR2615W4R70J]	4.7 Ohm [PWR6327N4R70JE]	4.7 uF [C1206C475K4RACT U]
4.7 Ohm [PWR1913W4R70J]	4.7 Ohm [PWR2615W4R70JE]	4.7 Ohm [PWR6327W4R70JE]	4.7 uF [C1206C475K5PACT U]
4.7 Ohm [PWR2010W4R70J E]	4.7 Ohm [PWR263S-20-4R70F]	4.7 uF [10TPU4R7MSI]	4.7 uF [C1206C475K8NAC TU]
4.7 Ohm [PWR220T-20-4R70F]	4.7 Ohm [PWR263S-20-4R70J]	4.7 uF [C0603C475K8PACT U]	4.7 uF [C1206C475K8PACT U]
4.7 Ohm [PWR220T-20-4R70J]	4.7 Ohm [PWR263S-20-4R70JE]	4.7 uF [C0603C475K9PACT U]	4.7 uF [C1206C475K8RACT U]
4.7 Ohm [PWR220T-35-4R70F]	4.7 Ohm [PWR263S-35-4R70F]	4.7 uF [C0805C475K3PACT U]	4.7 uF [C1206C475K9PACT U]
	4.7 Ohm [PWR263S-35-4R70FE]	4.7 uF [C0805C475K4PACT U]	

Multisim 14.1 Base Edition Components

4.7 uF [C1206C475K9RACT U]	4.7 uF [C1210C475K9RACT U]	4.7 uF [MDK15475K50B53 P3TUBE]	4.7 uF [T491C475M020AT]
4.7 uF [C1210C475K3NAC TU]	4.7 uF [C1210C475M4VAC TU]	4.7 uF [MDS10475K50A52 P3TUBE]	4.7 uF [T491C475M025AT]
4.7 uF [C1210C475K3PACT U]	4.7 uF [C1210C475M8VAC TU]	4.7 uF [T409D475M010AH 4250]	4.7 uF [T491C475M035AT]
4.7 uF [C1210C475K3RACT U]	4.7 uF [MDC10475K100A5 3P3TR32]	4.7 uF [T429C475M006AH 4250]	4.7 uF [T491D475M035AT]
4.7 uF [C1210C475K4PACT U]	4.7 uF [MDC10475K100A5 3P4TR32]	4.7 uF [T491A475M004AT]	4.7 uF [T491D475M050AT]
4.7 uF [C1210C475K4RACT U]	4.7 uF [MDC10475K100A5 4P3TUBE]	4.7 uF [T491A475M006AT]	4.7 uF [T491S475M006AT]
4.7 uF [C1210C475K5R1C7 186]	4.7 uF [MDC10475K100A5 4P4TUBE]	4.7 uF [T491A475M010AT]	4.7 uF [T491S475M010AT]
4.7 uF [C1210C475K5RACT U]	4.7 uF [MDC10475K100A5 4P3TUBE]	4.7 uF [T491A475M016AT]	4.7 uF [T491T475M016AT]
4.7 uF [C1210C475K8PACT U]	4.7 uF [MDC10475K50A52 P3TUBE]	4.7 uF [T491A475M016AT]	4.7 uF [T494A475M004AT]
4.7 uF [C1210C475K8RACT U]	4.7 uF [MDC10475K100B5 3P3TUBE]	4.7 uF [T491A475M020AT]	4.7 uF [T494A475M006AT]
4.7 uF [C1210C475K9PACT U]	4.7 uF [MDC15475K100B5 3P3TUBE]	4.7 uF [T491A475M025AT]	4.7 uF [T494A475M010AT]
	4.7 uF [MDK15475K50B53 P3TUBE]	4.7 uF [T491A475M016AT]	4.7 uF [T491T475M016AT]
	4.7 uF [MDK10475K50A52 P3TUBE]	4.7 uF [T491B475M010AT]	4.7 uF [T494A475M016AT]
		4.7 uF [T491B475M016AT]	4.7 uF [T494A475M020AT]
		4.7 uF [T491B475M020AT]	4.7 uF [T494A475M025AT]
		4.7 uF [T491B475M025AT]	4.7 uF [T494B475M010AT]

Multisim 14.1 Base Edition Components

4.7 uF [T494B475M016AT]	4.7 uF [T495C475M035AT E450]	4.7 uF [T540D475M063AH 6510]	4.7 uF [TAJC475K025RNJ]
4.7 uF [T494B475M020AT]	4.7 uF [T495C475M035AT E500]	4.7 uF [TACL475K004RTA]	4.7 uF [TAJC475K035RNJ]
4.7 uF [T494B475M025AT]	4.7 uF [T495C475M035AT E600]	4.7 uF [TACL475K006RTA]	4.7 uF [TAJC475K050RNJ]
4.7 uF [T494C475M020AT]	4.7 uF [T495D475M050AT E275]	4.7 uF [TACL475K010RTA]	4.7 uF [TAJD475K035RNJ]
4.7 uF [T494C475M025AT]	4.7 uF [T495D475M050AT E300]	4.7 uF [TAJA475K006RNJ]	4.7 uF [TAJD475K050RNJ]
4.7 uF [T494C475M035AT]	4.7 uF [T495D475M050AT E300]	4.7 uF [TAJA475K010RNJ]	4.7 uF [TAJK475K016RNJ]
4.7 uF [T494D475M035AT]	4.7 uF [T495X475M050AT E300]	4.7 uF [TAJA475K016RNJ]	4.7 uF [TAJP475K016RNJ]
4.7 uF [T494D475M050AT]	4.7 uF [T498A475M010AT E2K9]	4.7 uF [TAJA475K020RNJ]	4.7 uF [TAJR475K002RNJ]
4.7 uF [T494S475M006AT]	4.7 uF [T498B475M010AT E2K7]	4.7 uF [TAJA475K025RNJ]	4.7 uF [TAJR475K004RNJ]
4.7 uF [T494S475M010AT]	4.7 uF [T498B475M016AT E2K1]	4.7 uF [TAJB475K010RNJ]	4.7 uF [TAJR475K006RNJ]
4.7 uF [T494T475M016AT]	4.7 uF [T521D475M063AT E075]	4.7 uF [TAJB475K016RNJ]	4.7 uF [TAJR475K010RNJ]
4.7 uF [T495A475M010AT E1K3]	4.7 uF [T521D475M063AT E300]	4.7 uF [TAJB475K020RNJ]	4.7 uF [TAJS475K004RNJ]
4.7 uF [T495B475M016AT E700]		4.7 uF [TAJB475K025RNJ]	4.7 uF [TAJS475K006RNJ]
		4.7 uF [TAJB475K035RNJ]	4.7 uF [TAJS475K010RNJ]
		4.7 uF [TAJC475K020RNJ]	4.7 uF [TAJS475K016RNJ]

Multisim 14.1 Base Edition Components

4.7 uF [TAJT475K006RNJ]	4.7 uF [TPSB475K016R150 0]	4.7 uF [TPSD475K050R050 0]	4.7 uH [SDE1006A- 4R7M]
4.7 uF [TAJT475K010RNJ]	4.7 uF [TPSB475K020R100 0]	4.7 uF [TPSD475K050R070 0]	4.7 uH [SDR0302- 4R7ML]
4.7 uF [TAJT475K016RNJ]	4.7 uF [TPSB475K025R070 0]	4.7 uF [TPSR475K010R300 0]	4.7 uH [SDR0403- 4R7ML]
4.7 uF [TAJT475K020RNJ]	4.7 uF [TPSB475K025R090 0]	4.7 uF [TPSR475K010R500 0]	4.7 uH [SDR0603- 4R7ML]
4.7 uF [TAJW475K035RNJ]	4.7 uF [TPSB475K025R150 0]	4.7 uF [TPSS475K006R400 0]	4.7 uH [SDR0604- 4R7ML]
4.7 uF [THJA475K006RJN]	4.7 uF [TPSB475K035R150 0]	4.7 uF [TRJA475K020RRJ]	4.7 uH [SDR0703- 4R7ML]
4.7 uF [THJA475K016RJN]	4.7 uF [TPSC475K025R070 0]	4.7 uF [TRJB475K016RRJ]	4.7 uH [SDR0805- 4R7ML]
4.7 uF [THJB475K016RJN]	4.7 uF [TPSC475K035R060 0]	4.7 uF [TRJB475K035RRJ]	4.7 uH [SDR0906- 4R7ML]
4.7 uF [THJC475K035RJN]	4.7 uF [TPSC475K050R080 0]	4.7 uF [TRJC475K035RRJ]	4.7 uH [SDR1005- 4R7ML]
4.7 uF [THJD475K050RJN]	4.7 uF [TPSD475K035R070 0]	4.7 uF [TRJD475K050RRJ]	4.7 uH [SDR1006- 4R7ML]
4.7 uF [TPSA475K010R140 0]	4.7 uF [TPSD475K050R030 0]	4.7 uH [SDE0403A- 4R7M]	4.7 uH [SDR1030- 4R7M]
4.7 uF [TPSA475K016R200 0]		4.7 uH [SDE0604A- 4R7M]	4.7 uH [SDR1307- 4R7ML]
4.7 uF [TPSA475K020R180 0]		4.7 uH [SDE0805A- 4R7M]	4.7 uH [SDR1307A- 4R7M]
4.7 uF [TPSB475K016R080 0]			4.7 uH [SDR6603- 4R7M]
			4.7 uH [SDR7030- 4R7M]

Multisim 14.1 Base Edition Components

4.7 uH [SDR7045-4R7M]	4.7 uH [SRP1250-4R7M]	4.7 uH [SRR0604-4R7ML]	4.7 uH [SRR6603-4R7ML]
4.7 uH [SRN3010-4R7M]	4.7 uH [SRP1265A-4R7M]	4.7 uH [SRR0618-4R7ML]	4.7 uH [SRR7032-4R7M]
4.7 uH [SRN3015-4R7M]	4.7 uH [SRP1270-4R7M]	4.7 uH [SRR0906-4R7ML]	4.7 uH [SRR7045-4R7M]
4.7 uH [SRN4012T-4R7M]	4.7 uH [SRP1770TA-4R7M]	4.7 uH [SRR1003-4R7M]	4.7 uH [SRU1028-4R7Y]
4.7 uH [SRN4018-4R7M]	4.7 uH [SRP4012TA-4R7M]	4.7 uH [SRR1005-4R7M]	4.7 uH [SRU1028A-4R7Y]
4.7 uH [SRN4026-4R7M]	4.7 uH [SRP4020-4R7M]	4.7 uH [SRR1210-4R7Y]	4.7 uH [SRU1048-4R7Y]
4.7 uH [SRN5020-4R7M]	4.7 uH [SRP4020TA-4R7M]	4.7 uH [SRR1210A-4R7Y]	4.7 uH [SRU1048A-4R7Y]
4.7 uH [SRN5040-4R7M]	4.7 uH [SRP5015TA-4R7M]	4.7 uH [SRR1240-4R7M]	4.7 uH [SRU1063-4R7Y]
4.7 uH [SRN6028-4R7M]	4.7 uH [SRP5030T-4R7M]	4.7 uH [SRR1260-4R7Y]	4.7 uH [SRU2011-4R7Y]
4.7 uH [SRN6045-4R7Y]	4.7 uH [SRP5030TA-4R7M]	4.7 uH [SRR1260A-4R7Y]	4.7 uH [SRU2013-4R7Y]
4.7 uH [SRN8040-4R7Y]	4.7 uH [SRP6540-4R7M]	4.7 uH [SRR1280-4R7Y]	4.7 uH [SRU2016-4R7Y]
4.7 uH [SRP1038A-4R7M]	4.7 uH [SRP7028A-4R7M]	4.7 uH [SRR3011-4R7YL]	4.7 uH [SRU3011-4R7Y]
4.7 uH [SRP1040-4R7M]	4.7 uH [SRP7030-4R7FM]	4.7 uH [SRR4011-4R7YL]	4.7 uH [SRU3014-4R7Y]
4.7 uH [SRP1235-4R7M]	4.7 uH [SRP7050TA-4R7M]	4.7 uH [SRR4018-4R7Y]	4.7 uH [SRU3017-4R7Y]
4.7 uH [SRP1245A-4R7M]	4.7 uH [SRR0603-4R7ML]	4.7 uH [SRR4028-4R7Y]	4.7 uH [SRU5011-4R7Y]

Multisim 14.1 Base Edition Components

4.7 uH [SRU5016-4R7Y]	4.75 kOhm [CR0603-FX-4751GLF]	4.75 Ohm [CRL0805-FW-4R75ELF]	4.99 kOhm [CAY16-4991F4LF]
4.7 uH [SRU5018-4R7Y]	4.75 kOhm [CR0805-FX-4751ELF]	4.75 Ohm [CRM1206-FX-4R75ELF]	4.99 kOhm [CR0201-FW-4991GLF]
4.7 uH [SRU5028-4R7Y]	4.75 kOhm [CR1206-FX-4751ELF]	4.8 kOhm [4116R-1-482]	4.99 kOhm [CR0402-FX-4991GLF]
4.7 uH [SRU5028A-4R7Y]	4.75 kOhm [CRM0805-FX-4751ELF]	4.8 kOhm [4116R-1-482LF]	4.99 kOhm [CR0603-FX-4991ELF]
4.7 uH [SRU6011-4R7Y]	4.75 kOhm [CRM1206-FX-4751ELF]	4.87 kOhm [CR0201-FW-4871GLF]	4.99 kOhm [CR0805-FX-4991ELF]
4.7 uH [SRU6018-4R7Y]	4.75 kOhm [CRM2512-FX-4751ELF]	4.87 kOhm [CR0402-FX-4871GLF]	4.99 kOhm [CR1206-FX-4991ELF]
4.7 uH [SRU6025-4R7Y]	4.75 kOhm [CRM2512-FX-4751ELF]	4.87 kOhm [CR0603-FX-4871ELF]	4.99 kOhm [CRM1206-FX-4991ELF]
4.7 uH [SRU6025A-4R7Y]	4.75 kOhm [CRT0402-BY-4751GLF]	4.87 kOhm [CR0805-FX-4871ELF]	4.99 kOhm [CRM2512-FX-4991ELF]
4.7 uH [SRU8028-4R7Y]	4.75 kOhm [CRT0603-BW-4751ELF]	4.87 kOhm [CR1206-FX-4871ELF]	4.99 kOhm [CRT0402-BY-4991GLF]
4.7 uH [SRU8028A-4R7Y]	4.75 kOhm [CRT0603-BY-4751ELF]	4.87 kOhm [CRT0603-BY-4871ELF]	4.99 kOhm [CRT0603-BV-4991ELF]
4.7 uH [SRU8043-4R7Y]	4.75 kOhm [CRT0603-DZ-4751ELF]	4.87 kOhm [CRT1206-FZ-4871ELF]	4.99 kOhm [CRT0603-BY-4991ELF]
4.75 kOhm [CAT16-4751F4LF]	4.75 kOhm [CRT1206-DW-4751ELF]	4.99 kOhm [CAT16-4991F4LF]	
4.75 kOhm [CAY16-4751F4LF]			
4.75 kOhm [CR0402-FX-4751GLF]			
4.75 kOhm [CR0603-FX-4751ELF]			

Multisim 14.1 Base Edition Components

4.99 kOhm [CRT0603-FY-4991EAS]	40 mOhm [CRA2512-FZ-R040ELF]	40 Ohm [PWR220T-20-40R0F]	40.2 kOhm [CRT0603-BY-4022ELF]
4.99 kOhm [CRT0603-FY-4991ELF]	40 mOhm [CRA2512-JZ-R040ELF]	40 Ohm [PWR221T-30-40R0F]	40.2 kOhm [CRT0603-DW-4022ELF]
4.99 kOhm [CRT0805-BY-4991ELF]	40 mOhm [CRF2512-FZ-R040ELF]	40 Ohm [PWR263S-20-40R0J]	40.2 kOhm [CRT0805-BY-4022ELF]
4.99 kOhm [CRT0805-DY-4991ELF]	40 mOhm [CRL1206-FV-R040ELF]	40 Ohm [PWR263S-35-40R0F]	40.2 kOhm [CRT1206-BY-4022ELF]
4.99 MOhm [CHV0805-FX-4994ELF]	40 mOhm [PWR163S-25-R040JE]	40 Ohm [PWR263S-35-40R0J]	40.2 kOhm [CRT1206-FZ-4022ELF]
4.99 MOhm [CR0603-FX-4994ELF]	40 mOhm [PWR221T-30-R040J]	40.2 kOhm [CAT16-4022F4LF]	40.2 Ohm [CAT16-40R2F4LF]
4.99 Ohm [CRL1206-FW-4R99ELF]	40 mOhm [PWR4412-2SBR0400F]	40.2 kOhm [CR0402-FX-4022GLF]	40.2 Ohm [CAY16-40R2F4LF]
4.99 Ohm [CRM1206-FX-4R99ELF]	40 mOhm [PWR4412-2SCR0400F]	40.2 kOhm [CR0603-FX-4022ELF]	40.2 Ohm [CR0201-FW-40R2GLF]
4.99 Ohm [CRS2010-FW-4R99ELF]	40 Ohm [PWR163S-25-40R0F]	40.2 kOhm [CR0805-FX-4022ELF]	40.2 Ohm [CR0603-FX-40R2ELF]
4.99 Ohm [CRT0603-BY-4R99ELF]	40 Ohm [PWR163S-25-40R0FE]	40.2 kOhm [CR1206-FX-4022ELF]	40.2 Ohm [CR0805-FX-40R2ELF]
4 AMP	40 Ohm [PWR163S-25-40R0J]	40.2 kOhm [CRM2512-FX-4022ELF]	40.2 Ohm [CR1206-FX-40R2ELF]
40 kOhm [PWR221T-30-4002F]			40.2 Ohm [CRT0402-BY-40R2GLF]

Multisim 14.1 Base Edition Components

40.2 Ohm [CRT0402-FZ- 40R2GLF]	4000BD_15V	4002BP_5V	40106BD_15V
	4000BD_5V	4002BT_10V	40106BD_5V
40.2 Ohm [CRT0805-BY- 40R2ELF]	4000BP_10V	4002BT_15V	40106BP_10V
	4000BP_15V	4002BT_5V	40106BP_15V
	4000BP_5V	4008BD_10V	40106BP_5V
40.2 Ohm [CRT1206-BY- 40R2ELF]	4000BP_5V	4008BD_15V	40106BP_5V
	4000BT_10V	4008BD_5V	40106BT_10V
40_AMP	4000BT_15V	4008BP_10V	40106BT_15V
400 mOhm [PWR163S-25- R400FE]	4000BT_5V	4008BP_15V	40106BT_5V
	4001BD_10V	4008BP_5V	4010BC1_10V
400 mOhm [PWR220T-35- R400F]	4001BD_15V	4008BP_5V	4010BC1_15V
	4001BD_5V	4008BT_10V	4010BC1_5V
400 mOhm [PWR221T-30- R400F]	4001BP_10V	4008BT_15V	4010BEY_10V
	4001BP_15V	4008BT_5V	4010BEY_15V
	4001BP_5V	4009BCL_10V	4010BEY_5V
400 mOhm [PWR263S-35- R400F]	4001BP_5V	4009BCL_15V	4010BF_10V
	4001BT_10V	4009BCL_5V	4010BF_15V
400 nH [SRP7050TA-R40M]	4001BT_15V	4009BCP_10V	4010BF_5V
400 Ohm [4814P- T02-401]	4001BT_5V	4009BCP_15V	4010BF_5V
	4002BD_10V	4009BCP_5V	4010BM1_10V
400 Ohm [PWR163S-25- 4000F]	4002BD_15V	4009BCP_5V	4010BM1_15V
	4002BD_5V	4009BD_10V	4010BM1_5V
400 Ohm [PWR220T-35- 4000J]	4002BP_10V	4009BD_15V	4011BD_10V
	4002BP_15V	4009BD_5V	4011BD_15V
4000BD_10V	4002BP_5V	40106BD_10V	4011BD_5V

Multisim 14.1 Base Edition Components

4011BP_10V	4013BT_15V	4017BP_10V	402 kOhm [CR1206-FX-4023ELF]
4011BP_15V	4013BT_5V	4017BP_10V	
4011BP_5V	4014BD_10V	4017BP_15V	402 kOhm [CR2512-FX-4023ELF]
4011BP_5V	4014BD_15V	4017BP_5V	
4011BT_10V	4014BD_5V	4017BP_5V	402 kOhm [CRT0805-BY-4023ELF]
4011BT_15V	4014BP_10V	4017BT_10V	
4011BT_5V	4014BP_15V	4017BT_15V	
4012BD_10V	4014BP_5V	4017BT_5V	402 kOhm [CRT1206-BY-4023ELF]
4012BD_15V	4014BP_5V	4019BD_10V	
4012BD_5V	4014BT_10V	4019BD_15V	402 kOhm [CRT1206-FZ-4023ELF]
4012BP_10V	4014BT_15V	4019BD_5V	
4012BP_15V	4014BT_5V	4019BP_10V	402 Ohm [CR0402-FX-4020GLF]
4012BP_5V	4015BD_10V	4019BP_15V	
4012BP_5V	4015BD_15V	4019BP_5V	402 Ohm [CR0603-FX-4020ELF]
4012BT_10V	4015BD_5V	4019BP_5V	
4012BT_15V	4015BP_10V	4019BT_10V	402 Ohm [CR0805-FX-4020ELF]
4012BT_5V	4015BP_15V	4019BT_15V	
4013BD_10V	4015BP_5V	4019BT_5V	402 Ohm [CRT0402-FZ-4020GLF]
4013BD_15V	4015BP_5V	402 kOhm [CR0402-FX-4023GLF]	
4013BD_5V	4015BT_10V		
4013BP_10V	4015BT_15V	402 kOhm [CR0603-FX-4023ELF]	402 Ohm [CRT0603-BV-4020ELF]
4013BP_15V	4015BT_5V		
4013BP_5V	4017BD_10V		402 Ohm [CRT0805-BY-4020ELF]
4013BP_5V	4017BD_15V	402 kOhm [CR0805-FX-4023ELF]	
4013BT_10V	4017BD_5V		

Multisim 14.1 Base Edition Components

402 Ohm [PWR4318W4020FE]	4025BP_10V	4028BT_15V	4041BP_10V
	4025BP_15V	4028BT_5V	4041BP_15V
4023BD_10V	4025BP_5V	4030BD_10V	4041BP_5V
4023BD_15V	4025BP_5V	4030BD_15V	4041BP_5V
4023BD_5V	4025BT_10V	4030BD_5V	4041BT_10V
4023BP_10V	4025BT_15V	4030BP_10V	4041BT_15V
4023BP_15V	4025BT_5V	4030BP_15V	4041BT_5V
4023BP_5V	4027BD_10V	4030BP_5V	4042BD_10V
4023BP_5V	4027BD_15V	4030BP_5V	4042BD_15V
4023BT_10V	4027BD_5V	4030BT_10V	4042BD_5V
4023BT_15V	4027BP_10V	4030BT_15V	4042BP_10V
4023BT_5V	4027BP_15V	4030BT_5V	4042BP_15V
4024BD_10V	4027BP_5V	4040BD_10V	4042BP_5V
4024BD_15V	4027BP_5V	4040BD_15V	4042BP_5V
4024BD_5V	4027BT_10V	4040BD_5V	4042BT_10V
4024BP_10V	4027BT_15V	4040BP_10V	4042BT_15V
4024BP_15V	4027BT_5V	4040BP_15V	4042BT_5V
4024BP_5V	4028BD_10V	4040BP_5V	4043BD_10V
4024BP_5V	4028BD_15V	4040BP_5V	4043BD_15V
4024BT_10V	4028BD_5V	4040BT_10V	4043BD_5V
4024BT_15V	4028BP_10V	4040BT_15V	4043BP_10V
4024BT_5V	4028BP_15V	4040BT_5V	4043BP_15V
4025BD_10V	4028BP_5V	4041BD_10V	4043BP_5V
4025BD_15V	4028BP_5V	4041BD_15V	4043BP_5V
4025BD_5V	4028BT_10V	4041BD_5V	4043BT_10V

Multisim 14.1 Base Edition Components

4043BT_15V	4050BP_10V	4068BT_5V	4071BP_15V
4043BT_5V	4050BP_15V	4069BCL_10V	4071BP_5V
4044BD_10V	4050BP_5V	4069BCL_15V	4071BP_5V
4044BD_15V	4050BP_5V	4069BCL_5V	4071BT_10V
4044BD_5V	4050BT_10V	4069BCP_10V	4071BT_15V
4044BP_10V	4050BT_15V	4069BCP_15V	4071BT_5V
4044BP_15V	4050BT_5V	4069BCP_5V	4072BD_10V
4044BP_5V	4066BD_10V	4069BCP_5V	4072BD_15V
4044BP_5V	4066BD_15V	4069BD_10V	4072BD_5V
4044BT_10V	4066BD_5V	4069BD_15V	4072BP_10V
4044BT_15V	4066BP_10V	4069BD_5V	4072BP_15V
4044BT_5V	4066BP_15V	4070BD_10V	4072BP_5V
4049BD_10V	4066BP_5V	4070BD_15V	4072BP_5V
4049BD_15V	4066BT_10V	4070BD_5V	4072BT_10V
4049BD_5V	4066BT_15V	4070BP_10V	4072BT_15V
4049BP_10V	4066BT_5V	4070BP_15V	4072BT_5V
4049BP_15V	4068BD_10V	4070BP_5V	4073BD_10V
4049BP_5V	4068BD_15V	4070BP_5V	4073BD_15V
4049BP_5V	4068BD_5V	4070BT_10V	4073BD_5V
4049BT_10V	4068BP_10V	4070BT_15V	4073BP_10V
4049BT_15V	4068BP_15V	4070BT_5V	4073BP_15V
4049BT_5V	4068BP_5V	4071BD_10V	4073BP_5V
4050BD_10V	4068BP_5V	4071BD_15V	4073BP_5V
4050BD_15V	4068BT_10V	4071BD_5V	4073BT_10V
4050BD_5V	4068BT_15V	4071BP_10V	4073BT_15V

Multisim 14.1 Base Edition Components

4073BT_5V	4077BP_15V	4081BT_5V	4086BP_10V
4075BD_10V	4077BP_5V	4082BD_10V	4086BP_15V
4075BD_15V	4077BP_5V	4082BD_15V	4086BP_5V
4075BD_5V	4077BT_10V	4082BD_5V	4086BT_10V
4075BP_10V	4077BT_15V	4082BP_10V	4086BT_15V
4075BP_15V	4077BT_5V	4082BP_15V	4086BT_5V
4075BP_5V	4078BD_10V	4082BP_5V	4093BD_10V
4075BP_5V	4078BD_15V	4082BP_5V	4093BD_15V
4075BT_10V	4078BD_5V	4082BT_10V	4093BD_5V
4075BT_15V	4078BP_10V	4082BT_15V	4093BP_10V
4075BT_5V	4078BP_15V	4082BT_5V	4093BP_15V
4076BD_10V	4078BP_5V	4085BD_10V	4093BP_5V
4076BD_15V	4078BP_5V	4085BD_15V	4093BP_5V
4076BD_5V	4078BT_10V	4085BD_5V	4093BT_10V
4076BD_5V	4078BT_15V	4085BP_10V	4093BT_15V
4076BP_10V	4078BT_5V	4085BP_15V	4093BT_5V
4076BP_15V	4081BD_10V	4085BP_5V	41 kOhm [4608X-102-413LF]
4076BP_5V	4081BD_15V	4085BP_5V	41 kOhm [4609X-101-413LF]
4076BT_10V	4081BD_5V	4085BT_10V	41 kOhm [4610H-101-413LF]
4076BT_15V	4081BP_10V	4085BT_15V	41.2 kOhm [CR0402-FX-4122GLF]
4076BT_5V	4081BP_15V	4085BT_5V	41.2 kOhm [CR0603-FX-4122ELF]
4077BD_10V	4081BP_5V	4086BD_10V	
4077BD_15V	4081BP_5V	4086BD_15V	
4077BD_5V	4081BT_10V	4086BD_5V	
4077BP_10V	4081BT_15V	4086BD_5V	

Multisim 14.1 Base Edition Components

41.2 kOhm [CR0805-FX- 4122ELF]	4114R-3-302/622LF	4116R-3-221/391LF	412 kOhm [CR0805-FX- 4123ELF]
41.2 kOhm [CR1206-FX- 4122ELF]	4114R-3-331/391	4116R-3-302/622	412 kOhm [CR1206-FX- 4123ELF]
41.2 kOhm [CRT1206-BY- 4122ELF]	4114R-3-331/391LF	4116R-3-302/622LF	412 kOhm [CRM2512-FX- 4123ELF]
	4114R-3-331/471	4116R-3-330/390	
	4114R-3-331/471LF	4116R-3-331/391	
	4114R-3-331/681	4116R-3-331/391LF	
	4114R-3-331/681LF	4116R-3-331/471	
41.2 Ohm [CR0603- FX-41R2ELF]	4114R-3-361/781	4116R-3-331/471LF	412 Ohm [CR0402- FX-4120GLF]
41.2 Ohm [CR0805- FX-41R2ELF]	4114R-3-391/821	4116R-3-331/681	412 Ohm [CR0603- FX-4120ELF]
	4114R-3-750/621	4116R-3-331/681LF	
41.2 Ohm [CR1206- FX-41R2ELF]	4116R-3-121/201	4116R-3-361/781	412 Ohm [CR0805- FX-4120ELF]
	4116R-3-152/332	4116R-3-361/781LF	
4108R-3-121/121LF	4116R-3-152/332LF	4116R-3-391/821	412 Ohm [CR1206- FX-4120ELF]
4108R-3-221/221LF	4116R-3-161/241	4116R-3-391/821LF	412 Ohm [CRT1206-BY- 4120ELF]
4108R-3-221/331LF	4116R-3-161/241LF	4116R-3-431/821	
4114R-3-104/103	4116R-3-161/261	4116R-3-471/681	413990-1
4114R-3-121/201	4116R-3-161/261LF	4116R-3-471/681LF	
4114R-3-152/332	4116R-3-181/391	4116R-3-621/911	42.2 kOhm [CR0402-FX- 4222GLF]
4114R-3-161/261	4116R-3-181/391LF	4116R-3-621/911LF	
4114R-3-181/391	4116R-3-220/330	4116R-3-681/102	42.2 kOhm [CR0603-FX- 4222ELF]
4114R-3-181/391LF	4116R-3-221/271	4116R-3-681/681	
4114R-3-221/271	4116R-3-221/271LF	4116R-3-681/681LF	42.2 kOhm [CR0805-FX- 4222ELF]
4114R-3-221/331	4116R-3-221/331	4116R-3-820/131	
4114R-3-221/331LF	4116R-3-221/331LF	412 kOhm [CR0603-FX- 4123ELF]	42.2 kOhm [CR1206-FX- 4222ELF]
4114R-3-302/622	4116R-3-221/391		

Multisim 14.1 Base Edition Components

42.2 kOhm [CRT0402-FZ- 4222GLF]	422 Ohm [CR1206- FX-4220ELF]	43 mF [C0805C439KBGAC TU]	43 Ohm [CR0402- FX-43R0GLF]
42.2 Ohm [CR0402- FX-42R2GLF]	422 Ohm [CRT0402-FZ- 4220GLF]	43 Ohm [4116R-1- 430]	43 Ohm [CR0402- JW-430GLF]
42.2 Ohm [CR0603- FX-42R2ELF]	43 kOhm [4116R-1- 433]	43 Ohm [4116R-2- 430]	43 Ohm [CR0603- FX-43R0ELF]
42.2 Ohm [CR0805- FX-42R2ELF]	43 kOhm [CAT16- 433J4LF]	43 Ohm [4116R-2- 430LF]	43 Ohm [CR0603- JW-430ELF]
42.2 Ohm [CR0805- FX-42R2GLF]	43 kOhm [CAY16- 433J4LF]	43 Ohm [4308R- 102-430LF]	43 Ohm [CR0805- FX-43R0ELF]
42.2 Ohm [CR1206- FX-42R2ELF]	43 kOhm [CAY17- 433JALF]	43 Ohm [4310R- 102-430]	43 Ohm [CR0805- FX-43R0GLF]
422 kOhm [CR0402-FX- 4223GLF]	43 kOhm [CR0201- FW-4302GLF]	43 Ohm [4420P-1- 430]	43 Ohm [CR0805- JW-430ELF]
422 kOhm [CR0603-FX- 4223ELF]	43 kOhm [CR0402- FX-4302GLF]	43 Ohm [4816P-1- 430]	43 Ohm [CR1206- FX-43R0ELF]
422 kOhm [CR0805-FX- 4223ELF]	43 kOhm [CR0603- FX-4302ELF]	43 Ohm [4816P-1- 430LF]	43 Ohm [CR1206- JW-430ELF]
422 kOhm [CR1206-FX- 4223ELF]	43 kOhm [CR0603- JW-433ELF]	43 Ohm [CAT10- 430J4LF]	43 Ohm [CRM2512-FX- 43R0ELF]
422 kOhm [CR1206-FX- 4223ELF]	43 kOhm [CR0805- FX-4302ELF]	43 Ohm [CAT16- 430J4LF]	43 pF [C0805C430KBGAC TU]
422 Ohm [CR0402- FX-4220GLF]	43 kOhm [CR0805- JW-433ELF]	43 Ohm [CAT25- 430JALF]	43 pF [C1206C430KBGAC TU]
422 Ohm [CR0603- FX-4220ELF]	43 kOhm [CR1206- FX-4302ELF]	43 Ohm [CAY10- 430J4LF]	43 pF [C1210C430KBGAC TU]
422 Ohm [CR0805- FX-4220ELF]	43 kOhm [CR1206- JW-433ELF]	43 Ohm [CAY16- 430J4LF]	
	43 kOhm [CRM2512-JW- 433ELF]	43 Ohm [CAY16- 43R0F4LF]	

Multisim 14.1 Base Edition Components

43 pF [C1812C430KBGAC TU]	43.2 Ohm [CR1206- FX-43R2ELF]	430 mOhm [CRL0603-JW- R430ELF]	430 Ohm [4310R- 102-431]
43 pF [C1825C430KBGAC TU]	43.2 Ohm [CR2010- FX-43R2ELF]	430 mOhm [CRL0805-FW- R430ELF]	430 Ohm [4608X- 102-431LF]
43 pF [C2220C430KBGAC TU]	43.2 Ohm [CRM2512-FX- 43R2ELF]	430 mOhm [CRL0805-JW- R430ELF]	430 Ohm [4816P-1- 431]
43 pF [C2225C430KBGAC TU]	430 kOhm [CAY16- 434J4LF]	430 mOhm [CRL1206-FW- R430ELF]	430 Ohm [4816P-1- 431LF]
43.2 kOhm [CR0402-FX- 4322GLF]	430 kOhm [CR0402-FX- 4303GLF]	430 mOhm [CRL1206-JW- R430ELF]	430 Ohm [4816P-2- 431]
43.2 kOhm [CR0603-FX- 4322ELF]	430 kOhm [CR0603-FX- 4303ELF]	430 mOhm [CRL1206-JW- R430ELF]	430 Ohm [4816P-2- 431LF]
43.2 kOhm [CR0805-FX- 4322ELF]	430 kOhm [CR0603-JW- 434ELF]	430 mOhm [CRL2010-FW- R430ELF]	430 Ohm [4816P- T01-431LF]
43.2 kOhm [CR1206-FX- 4322ELF]	430 kOhm [CR0805-FX- 4303ELF]	430 mOhm [CRL2010-JW- R430ELF]	430 Ohm [4816P- T02-431]
43.2 Ohm [CR0402- FX-43R2GLF]	430 kOhm [CR0805-JW- 434ELF]	430 mOhm [CRL2512-FW- R430ELF]	430 Ohm [4816P- T02-431LF]
43.2 Ohm [CR0603- FX-43R2ELF]	430 kOhm [CR1206-FX- 4303ELF]	430 mOhm [CRL2512-JW- R430ELF]	430 Ohm [CAT16- 431J4LF]
43.2 Ohm [CR0603- FX-43R2GLF]	430 kOhm [CR1206-JW- 434ELF]	430 mOhm [CRM2512-FX- R430ELF]	430 Ohm [CAT25- 431JALF]
43.2 Ohm [CR0805- FX-43R2ELF]	430 mOhm [CRL0603-FW- R430ELF]	430 Ohm [4116R-1- 431]	430 Ohm [CAY16- 431J4LF]
		430 Ohm [4308R- 102-431]	430 Ohm [CR0201- FW-4300GLF]
			430 Ohm [CR0402- FX-4300GLF]

Multisim 14.1 Base Edition Components

430 Ohm [CR0402-JW-431GLF]	430 pF [C0603C431K3HACT U]	4304M-104-161/111L	4306R-104-810/131
430 Ohm [CR0603-FX-4300ELF]	430 pF [C0603C431K5HACT U]	4304M-104-221/331	4306R-104-810/131L
430 Ohm [CR0603-JW-431ELF]	430 pF [C1206C431KBGAC TU]	4304M-104-221/331L	4308H-104-181/391
430 Ohm [CR0805-FX-4300ELF]	430 pF [C1210C431KBGAC TU]	4306R-104-121/191	4308H-104-181/391L
430 Ohm [CR0805-JW-431ELF]	430 pF [C1812C431KBGAC TU]	4306R-104-121/201	4308H-104-221/331
430 Ohm [CR1206-FX-4300ELF]	430 pF [C1825C431KBGAC TU]	4306R-104-161/241	4308H-104-221/331L
430 Ohm [CR1206-JW-431ELF]	430 pF [C2220C431KBGAC TU]	4306R-104-161/241L	4308M-104-221/331
430 Ohm [CR2010-JW-431ELF]	430 pF [C2225C431KBGAC TU]	4306R-104-180/390	4308M-104-221/331L
430 Ohm [CR2512-JW-431ELF]	430 pF [C2225C431KBGAC TU]	4306R-104-181/391	4308M-104-221/331L
430 pF [C0402C431K1HACT U]	4304M-104-121/191	4306R-104-181/391L	4308M-104-331/471
430 pF [C0402C431K3HACT U]	4304M-104-121/191L	4306R-104-221/271L	4308M-104-331/471L
430 pF [C0402C431K5HACT U]	4304M-104-121/191L	4306R-104-221/331	4308R-104-102/202
430 pF [C0603C431K1HACT U]	4304M-104-121/481	4306R-104-221/331L	4308R-104-103/203
	4304M-104-161/111	4306R-104-302/622	4308R-104-103/203L
		4306R-104-302/622L	4308R-104-112/112
		4306R-104-331/391	4308R-104-112/112L
		4306R-104-331/391L	4308R-104-121/131
		4306R-104-331/471	4308R-104-152/332
		4306R-104-331/471L	4308R-104-161/241

Multisim 14.1 Base Edition Components

4308R-104- 161/241L	4308R-104- 331/681L	4310H-104- 331/471	4310M-104- 331/471L
4308R-104-161/261	4308R-104-332/472	4310H-104- 331/471L	4310M-104- 820/820
4308R-104-181/241	4308R-104-681/102	4310H-104- 331/681	4310M-104- 820/820L
4308R-104- 181/241L	4308R-104- 810/131	4310H-104- 331/681	4310R-104-111/221
4308R-104-181/391	4308R-104- 810/131L	4310H-104- 471/102L	4310R-104- 111/221L
4308R-104- 181/391L	4308R-104-820/131	4310H-104- 820/131	4310R-104-121/181
4308R-104-221/271	4308R-104- 820/131L	4310M-104- 181/391	4310R-104-121/191
4308R-104-221/331	4310H-104- 161/241	4310M-104- 181/391L	4310R-104-152/332
4308R-104- 221/331L	4310H-104- 161/241L	4310M-104- 221/151	4310R-104- 152/332L
4308R-104-271/271	4310H-104- 181/391	4310M-104- 221/151L	4310R-104-161/241
4308R-104-302/622	4310H-104- 181/391L	4310M-104- 221/331	4310R-104- 161/241L
4308R-104- 302/622L	4310H-104- 221/271	4310M-104- 221/331L	4310R-104-161/261
4308R-104-331/331	4310H-104- 221/271L	4310M-104- 271/391	4310R-104-181/221
4308R-104- 331/331L	4310H-104- 221/331	4310M-104- 302/622	4310R-104-181/241
4308R-104-331/391	4310H-104- 221/331L	4310M-104- 302/622L	4310R-104-181/331
4308R-104- 331/391L	4310H-104- 221/800	4310M-104- 331/471	4310R-104-181/391
4308R-104-331/471	4310H-104- 221/800L		4310R-104- 181/391L
4308R-104- 331/471L			4310R-104-181/681
4308R-104-331/681			

Multisim 14.1 Base Edition Components

4310R-104-181/681L	4310R-104-391/561	432 kOhm [CR0805-FX-4323ELF]	44.2 kOhm [CRM2512-FX-4422ELF]
4310R-104-221/181	4310R-104-391/561L	432 kOhm [CR1206-FX-4323ELF]	44.2 kOhm [PWR163S-25-4422JE]
4310R-104-221/182L	4310R-104-391/581	432 Ohm [CR0402-FX-4320GLF]	44.2 Ohm [CR0402-FX-44R2GLF]
4310R-104-221/271	4310R-104-391/681	432 Ohm [CR0603-FX-4320ELF]	44.2 Ohm [CR0603-FX-44R2ELF]
4310R-104-221/271L	4310R-104-471/681	432 Ohm [CR0805-FX-4320ELF]	44.2 Ohm [CR0805-FX-44R2ELF]
4310R-104-221/331	4310R-104-471/681L	432 Ohm [CR1206-FX-4320ELF]	44.2 Ohm [CR1206-FX-44R2ELF]
4310R-104-221/331L	4310R-104-501/501	432 Ohm [CR2512-FX-4320ELF]	442 kOhm [CR0402-FX-4423GLF]
4310R-104-271/271	4310R-104-681/102	432 Ohm [CRM2512-FX-4320ELF]	442 kOhm [CR0603-FX-4423ELF]
4310R-104-271/271L	4310R-104-810/131	44.2 kOhm [CR0402-FX-4422GLF]	442 kOhm [CR0805-FX-4423ELF]
4310R-104-272/472	4310R-104-820/131	44.2 kOhm [CR0603-FX-4422ELF]	442 kOhm [CR1206-FX-4423ELF]
4310R-104-302/622	4310R-104-820/131L	44.2 kOhm [CR0805-FX-4422ELF]	442 Ohm [CR0402-FX-4420GLF]
4310R-104-302/622L	4311R-104-161/241	44.2 kOhm [CR1206-FX-4422ELF]	442 Ohm [CR0603-FX-4420ELF]
4310R-104-330/470	4311R-104-161/241L	44.2 kOhm [CRM2512-FX-4320ELF]	442 Ohm [CR0805-FX-4420ELF]
4310R-104-331/391	4311R-104-221/331	44.2 kOhm [CR0402-FX-4422GLF]	
4310R-104-331/391L	4311R-104-221/331L	44.2 kOhm [CR0603-FX-4422ELF]	
4310R-104-331/471	4311R-104-331/471	44.2 kOhm [CR0805-FX-4422ELF]	
4310R-104-331/471L	4311R-104-331/471L	44.2 kOhm [CR1206-FX-4422ELF]	
4310R-104-331/681	432 kOhm	44.2 kOhm [CR1206-FX-4422ELF]	
4310R-104-331/681L	[CR0603-FX-4323ELF]	442 Ohm [CR0805-FX-4420ELF]	

Multisim 14.1 Base Edition Components

442 Ohm [CR1206-FX-4420ELF]	45.3 kOhm [CR1206-FX-4532ELF]	4502BP_5V	4510BD_10V
442 Ohm [CRT0402-FZ-4420GLF]	45.3 kOhm [CRM2512-FX-4532ELF]	4502BP_15V	4510BD_15V
4420P-3-221/331	45.3 kOhm [CRT0603-BY-4532ELF]	4502BT_10V	4510BD_5V
4420P-3-302/622	45.3 kOhm [CRT0603-BY-4532ELF]	4502BT_15V	4510BP_10V
4420P-3-302/622LF	45.3 Ohm [CR0201-FW-45R3GLF]	4502BT_5V	4510BP_15V
4420P-3-331/391	45.3 Ohm [CR0402-FX-45R3GLF]	4503BCL_10V	4510BP_5V
4420P-3-331/471	45.3 Ohm [CR0402-FX-45R3GLF]	4503BCL_15V	4510BP_5V
4420P-3-331/471LF	45.3 Ohm [CR0603-FX-45R3ELF]	4503BCL_5V	4510BT_10V
4420P-T03-221/271	45.3 Ohm [CR0805-FX-45R3ELF]	4503BCP_10V	4510BT_15V
4420P-T03-312/182	45.3 Ohm [CR0805-FX-45R3ELF]	4503BCP_15V	4510BT_5V
4420P-T03-330/390	45.3 Ohm [CR1206-FX-45R3ELF]	4503BCP_5V	4511BD_10V
4420P-T03-330/470	45.3 Ohm [CR1206-FX-45R3ELF]	4503BD_10V	4511BD_15V
4420P-T03-331/471	45.3 Ohm [CR2010-FX-45R3ELF]	4503BD_15V	4511BD_5V
45 mOhm [CRA2512-JZ-R045ELF]	45.3 Ohm [CRT0805-BY-45R3ELF]	4503BD_5V	4511BP_10V
45.3 kOhm [CR0402-FX-4532GLF]	450 nH [SRP1038A-R45M]	4508BD_10V	4511BP_15V
45.3 kOhm [CR0603-FX-4532ELF]	4502BD_10V	4508BD_15V	4511BP_5V
45.3 kOhm [CR0805-FX-4532ELF]	4502BD_15V	4508BD_5V	4511BT_10V
	4502BD_5V	4508BP_10V	4511BT_15V
	4502BP_10V	4508BP_15V	4511BT_5V
	4502BP_15V	4508BP_5V	4512BD_10V
		4508BP_5V	4512BD_15V
		4508BT_10V	4512BD_5V
		4508BT_15V	4512BP_10V
		4508BT_5V	4512BP_15V

Multisim 14.1 Base Edition Components

4512BP_5V	4516BD_10V	4520BP_5V	453 Ohm [CRT1206-BY- 4530ELF]
4512BP_5V	4516BD_15V	4520BP_5V	4532BD_10V
4512BT_10V	4516BD_5V	4520BT_10V	4532BD_15V
4512BT_15V	4516BP_10V	4520BT_15V	4532BD_5V
4512BT_5V	4516BP_15V	4520BT_5V	4532BP_10V
4514BD_10V	4516BP_5V	453 kOhm [CR0402-FX- 4533GLF]	4532BP_15V
4514BD_15V	4516BP_5V	453 kOhm [CR0603-FX- 4533ELF]	4532BP_5V
4514BD_5V	4516BT_10V	453 kOhm [CR0805-FX- 4533ELF]	4532BT_10V
4514BP_10V	4516BT_15V	453 kOhm [CR1206-FX- 4533ELF]	4532BT_15V
4514BP_15V	4516BT_5V	453 Ohm [CAY16- 4530F4LF]	4532BT_5V
4514BP_5V	4518BD_10V	453 Ohm [CR0402- FX-4530GLF]	4556BD_10V
4514BP_5V	4518BD_15V	453 Ohm [CR0603- FX-4530ELF]	4556BD_15V
4514BT_10V	4518BD_5V	453 Ohm [CR0805- FX-4530ELF]	4556BD_5V
4514BT_15V	4518BP_10V	453 Ohm [CRM2512-FX- 4530ELF]	4556BP_10V
4514BT_5V	4518BP_15V	453 Ohm [CRM2512-FX- 4530ELF]	4556BP_15V
4515BD_10V	4518BP_5V	453 Ohm [CRM2512-FX- 4530ELF]	4556BP_5V
4515BD_15V	4518BP_5V	453 Ohm [CRM2512-FX- 4530ELF]	4556BT_10V
4515BD_5V	4518BT_10V	453 Ohm [CRM2512-FX- 4530ELF]	4556BT_15V
4515BP_10V	4518BT_15V	453 Ohm [CRM2512-FX- 4530ELF]	4556BT_5V
4515BP_15V	4518BT_5V	453 Ohm [CRM2512-FX- 4530ELF]	4585BD_15V
4515BP_5V	4520BD_10V	453 Ohm [CRM2512-FX- 4530ELF]	4585BD_5V
4515BP_5V	4520BD_15V	453 Ohm [CRM2512-FX- 4530ELF]	4585BP_15V
4515BT_10V	4520BD_5V	453 Ohm [CRM2512-FX- 4530ELF]	
4515BT_15V	4520BP_10V	453 Ohm [CRM2512-FX- 4530ELF]	
4515BT_5V	4520BP_15V	453 Ohm [CRM2512-FX- 4530ELF]	

Multisim 14.1 Base Edition Components

4585BP_5V	46.4 Ohm [CR0805-FX-46R4ELF]	4608H-104-500/500L	4609X-104-331/391L
4585BT_15V			
4585BT_5V	46.4 Ohm [CR1206-FX-46R4ELF]	4608M-104-221/331L	4609X-104-331/471L
45970-4185			
46.4 kOhm [CR0402-FX-4642GLF]	46.4 Ohm [CRT0402-FZ-46R4GLF]	4608M-104-331/471L	4610H-104-101/101L
46.4 kOhm [CR0603-FX-4642ELF]	4604X-104-161/241L	4608X-104-161/241L	4610H-104-102/104L
46.4 kOhm [CR0603-FX-4642ELF]	4605X-104-331/391L	4608X-104-181/391L	4610H-104-221/331L
46.4 kOhm [CR0805-FX-4642ELF]	4606X-104-161/241L	4608X-104-220/330L	4610H-104-331/471L
46.4 kOhm [CR1206-FX-4642ELF]	4606X-104-181/391L	4608X-104-221/271L	4610M-104-121/281L
46.4 kOhm [CRT0402-BY-4642GLF]	4606X-104-221/271L	4608X-104-221/331L	4610M-104-131/131L
46.4 kOhm [CRT0402-FZ-4642GLF]	4606X-104-221/331L	4608X-104-302/622L	4610M-104-151/121L
46.4 kOhm [CRT0603-PW-4642ELF]	4606X-104-302/622L	4608X-104-331/221L	4610M-104-253/503L
46.4 kOhm [CRT0805-BY-4642ELF]	4606X-104-331/391L	4608X-104-331/391L	4610M-104-331/471L
46.4 kOhm [CR0402-FX-46R4GLF]	4606X-104-331/471L	4608X-104-331/471L	4610X-104-102/102L
46.4 kOhm [CR0603-FX-46R4GLF]	4606X-104-331/471L	4608X-104-332/472L	4610X-104-102/152L
46.4 kOhm [CR0805-FX-46R4GLF]	4607X-104-221/331L	4608X-104-471/681L	4610X-104-102/681L
46.4 Ohm [CR0402-FX-46R4GLF]	4608H-104-101/101L	4608X-104-810/131L	4610X-104-104/204L

Multisim 14.1 Base Edition Components

4610X-104- 122/242L	4610X-104- 302/622L	4612X-104- 181/391L	464 Ohm [CR0805- FX-4640ELF]
4610X-104- 151/181L	4610X-104- 330/470L	4612X-104- 221/331L	464 Ohm [CR1206- FX-4640ELF]
4610X-104- 152/222L	4610X-104- 331/391L	4612X-104- 331/471L	464 Ohm [CRT0402-FZ- 4640GLF]
4610X-104- 152/332L	4610X-104- 331/470L	4612X-104- 471/152L	464 Ohm [CRT0805-BY- 4640ELF]
4610X-104- 161/241L	4610X-104- 331/471L	4614X-104- 221/182L	464 Ohm [CRT1206-BY- 4640ELF]
4610X-104- 162/260L	4610X-104- 331/681L	4614X-104- 331/471L	464 Ohm [CRT1206-BY- 4640ELF]
4610X-104- 181/271L	4610X-104- 361/781L	464 kOhm [CR0402-FX- 4643GLF]	4-644456-0 46765-1001
4610X-104- 181/391L	4610X-104- 471/681L	464 kOhm [CR0603-FX- 4643ELF]	46765-2001
4610X-104- 221/182L	4610X-104- 681/102L	464 kOhm [CR0805-FX- 4643ELF]	47 kOhm [4108R-1- 473LF]
4610X-104- 221/271L	4610X-104- 810/131L	464 kOhm [CR1206-FX- 4643ELF]	47 kOhm [4114R-1- 473]
4610X-104- 221/331L	4610X-104- 821/561L	464 kOhm [CR1206-FX- 4643ELF]	47 kOhm [4114R-1- 473LF]
4610X-104- 222/332L	4611X-104- 161/241L	464 kOhm [CRT0603-BY- 4643ELF]	47 kOhm [4114R-2- 473]
4610X-104- 222/333L	4611X-104- 221/331L	464 Ohm [CAY16- 4640F4LF]	47 kOhm [4116R-1- 473]
4610X-104- 224/331L	4611X-104- 302/622L	464 Ohm [CR0603- FX-4640ELF]	47 kOhm [4116R-1- 473LF]
4610X-104- 272/472L	4611X-104- 331/471L		

Multisim 14.1 Base Edition Components

47 kOhm [4116R-2-473]	47 kOhm [4308M-101-473LF]	47 kOhm [4310M-102-473]	47 kOhm [4420P-2-473]
47 kOhm [4116R-2-473LF]	47 kOhm [4308M-102-473]	47 kOhm [4310M-102-473LF]	47 kOhm [4420P-T01-473]
47 kOhm [4306H-101-473]	47 kOhm [4308M-102-473LF]	47 kOhm [4310R-101-473]	47 kOhm [4420P-T02-473]
47 kOhm [4306H-101-473LF]	47 kOhm [4308R-101-473]	47 kOhm [4310R-101-473LF]	47 kOhm [4604H-101-473LF]
47 kOhm [4306M-101-473]	47 kOhm [4308R-101-473LF]	47 kOhm [4310R-102-473]	47 kOhm [4604X-101-473LF]
47 kOhm [4306M-101-473LF]	47 kOhm [4308R-102-473]	47 kOhm [4310R-102-473LF]	47 kOhm [4604X-102-473LF]
47 kOhm [4306M-102-473]	47 kOhm [4308R-102-473LF]	47 kOhm [4416P-1-473]	47 kOhm [4604X-AP1-473LF]
47 kOhm [4306M-102-473LF]	47 kOhm [4309R-101-473]	47 kOhm [4416P-1-473LF]	47 kOhm [4605X-101-473LF]
47 kOhm [4306R-101-473]	47 kOhm [4309R-101-473LF]	47 kOhm [4416P-2-473]	47 kOhm [4605X-AP1-473LF]
47 kOhm [4306R-101-473LF]	47 kOhm [4310H-101-473]	47 kOhm [4416P-2-473LF]	47 kOhm [4606H-102-473LF]
47 kOhm [4306R-102-473]	47 kOhm [4310H-101-473LF]	47 kOhm [4416P-T01-473]	47 kOhm [4606M-101-473LF]
47 kOhm [4306R-102-473LF]	47 kOhm [4310H-102-473]	47 kOhm [4416P-T01-473LF]	47 kOhm [4606M-102-473LF]
47 kOhm [4308H-101-473]	47 kOhm [4310H-102-473LF]	47 kOhm [4416P-T02-473]	47 kOhm [4606X-101-473LF]
47 kOhm [4308H-102-473]	47 kOhm [4310M-101-473]	47 kOhm [4420P-1-473]	47 kOhm [4606X-102-473LF]
47 kOhm [4308M-101-473]	47 kOhm [4310M-101-473LF]	47 kOhm [4420P-1-473LF]	47 kOhm [4606X-AP1-473LF]

Multisim 14.1 Base Edition Components

47 kOhm [4606X-AP2-473LF]	47 kOhm [4610H-102-473LF]	47 kOhm [4814P-2-473LF]	47 kOhm [4818P-2-473LF]
47 kOhm [4607M-101-473LF]	47 kOhm [4610M-101-473LF]	47 kOhm [4814P-T01-473]	47 kOhm [4818P-T01-473]
47 kOhm [4607X-101-473LF]	47 kOhm [4610M-102-473LF]	47 kOhm [4814P-T01-473LF]	47 kOhm [4818P-T02-473]
47 kOhm [4608H-101-473LF]	47 kOhm [4610X-101-473LF]	47 kOhm [4814P-T02-473]	47 kOhm [4820P-1-473]
47 kOhm [4608H-102-473LF]	47 kOhm [4610X-102-473LF]	47 kOhm [4814P-T02-473LF]	47 kOhm [4820P-1-473LF]
47 kOhm [4608M-101-473LF]	47 kOhm [4610X-AP1-473LF]	47 kOhm [4816P-1-473]	47 kOhm [4820P-2-473]
47 kOhm [4608M-102-473LF]	47 kOhm [4610X-AP2-473LF]	47 kOhm [4816P-1-473LF]	47 kOhm [4820P-T01-473]
47 kOhm [4608X-101-473LF]	47 kOhm [4611X-101-473LF]	47 kOhm [4816P-2-473]	47 kOhm [4820P-T02-473]
47 kOhm [4608X-102-473LF]	47 kOhm [4612X-101-473LF]	47 kOhm [4816P-2-473LF]	47 kOhm [CAT10-473J4LF]
47 kOhm [4608X-AP1-473LF]	47 kOhm [4612X-102-473LF]	47 kOhm [4816P-T01-473]	47 kOhm [CAT16-4702F4LF]
47 kOhm [4608X-AP2-473LF]	47 kOhm [4614X-101-473LF]	47 kOhm [4816P-T01-473LF]	47 kOhm [CAT16-4702F8LF]
47 kOhm [4609H-101-473LF]	47 kOhm [4614X-102-473LF]	47 kOhm [4816P-T02-473]	47 kOhm [CAT16-473J2LF]
47 kOhm [4609M-101-473LF]	47 kOhm [4814P-1-473]	47 kOhm [4816P-T02-473LF]	47 kOhm [CAT16-473J4LF]
47 kOhm [4609X-101-473LF]	47 kOhm [4814P-1-473LF]	47 kOhm [4818P-1-473LF]	47 kOhm [CAT16-473J8LF]
47 kOhm [4609X-AP1-473LF]	47 kOhm [4814P-2-473]	47 kOhm [4818P-2-473]	47 kOhm [CAT25-473JALF]

Multisim 14.1 Base Edition Components

47 kOhm [CAY10-473J4LF]	47 kOhm [CR0805-JW-473ELF]	47 kOhm [CRT1206-FX-4702ELF]	47 mOhm [PWR4525WR047J]
47 kOhm [CAY16-4702F4LF]	47 kOhm [CR0805-JW-473GLF]	47 kOhm [PWR263S-20-4702JE]	47 mOhm [PWR4525WR047JE]
47 kOhm [CAY16-473J2LF]	47 kOhm [CR1206-FX-4702ELF]	47 mF [C0805C479KBGAC TU]	47 nF [03066C473KAT2A]
47 kOhm [CAY16-473J4GLF]	47 kOhm [CR1206-JW-473ELF]	47 mF [C1206C479K1GACT U]	47 nF [0306YC473KAT2A]
47 kOhm [CAY16-473J4LF]	47 kOhm [CR1206-JW-473GLF]	47 mOhm [CRM1206-FX-R047ELF]	47 nF [05083C473KAT2V]
47 kOhm [CAY16-473J8LF]	47 kOhm [CR2512-JW-473ELF]	47 mOhm [CRM2010-FX-R047ELF]	47 nF [05085C473KAT2A]
47 kOhm [CAY17-473JALF]	47 kOhm [CRM2010-FX-4702ELF]	47 mOhm [CRM2010-FX-R047ELF]	47 nF [06123C473KAT2S]
47 kOhm [CR0201-FW-4702GLF]	47 kOhm [CRM2010-JW-473ELF]	47 mOhm [CRM2010-JX-R047ELF]	47 nF [06125C473KAT2W]
47 kOhm [CR0402-FX-4702GLF]	47 kOhm [CRM2512-FX-4702ELF]	47 mOhm [CRM2512-FX-R047ELF]	47 nF [0612YC473KAT2S]
47 kOhm [CR0402-JW-473GLF]	47 kOhm [CRM2512-JW-473ELF]	47 mOhm [PWR1913WR047F]	47 nF [C0402C473K3RACT U]
47 kOhm [CR0603-FX-4702ELF]	47 kOhm [CRM2512-FX-473ELF]	47 mOhm [PWR1913WR047F E]	47 nF [C0402C473K4PACT U]
47 kOhm [CR0603-FX-4702HLF]	47 kOhm [CRT0402-DY-4702GLF]	47 mOhm [PWR2615WR047F]	47 nF [C0402C473K4RACT U]
47 kOhm [CR0603-JW-473ELF]	47 kOhm [CRT0805-BY-4702ELF]	47 mOhm [PWR2615WR047F E]	
47 kOhm [CR0603-JW-473GLF]	47 kOhm [CRT1206-BY-4702ELF]		

Multisim 14.1 Base Edition Components

47 nF [C0402C473K8PACT U]	47 nF [C0603C473M3VAC TU]	47 nF [C1206C473K1HACT U]	47 nF [C1206F473K3RACT U]
47 nF [C0402C473K8RACT U]	47 nF [C0805C473K1RACT U]	47 nF [C1206C473K1RACT U]	47 nF [C1206F473K4RACT U]
47 nF [C0402C473K9PACT U]	47 nF [C0805C473K3RACT U]	47 nF [C1206C473K3GACT U]	47 nF [C1206F473K5RACT U]
47 nF [C0402C473K9RACT U]	47 nF [C0805C473K4RACT U]	47 nF [C1206C473K3HACT U]	47 nF [C1210C473K1GACT U]
47 nF [C0603C473K1RACT U]	47 nF [C0805C473K5RACT U]	47 nF [C1206C473K3RACT U]	47 nF [C1210C473K1HACT U]
47 nF [C0603C473K3NAC TU]	47 nF [C0805C473K8RACT U]	47 nF [C1206C473K4RACT U]	47 nF [C1210C473K1RACT U]
47 nF [C0603C473K3RACT U]	47 nF [C0805C473M5UAC TU]	47 nF [C1206C473K5HACT U]	47 nF [C1210C473K2RACT U]
47 nF [C0603C473K4RACT U]	47 nF [C0805C473M5VAC TU]	47 nF [C1206C473K5RACT U]	47 nF [C1210C473K3GACT U]
47 nF [C0603C473K5NAC TU]	47 nF [C0805F473K3RACT U]	47 nF [C1206C473KARACT U]	47 nF [C1210C473K3HACT U]
47 nF [C0603C473K5RACT U]	47 nF [C0805F473K4RACT U]	47 nF [C1206C473M5UAC TU]	47 nF [C1210C473K5GACT U]
47 nF [C0603C473K8RACT U]	47 nF [C0805F473K5RACT U]	47 nF [C1206F473K1RACT U]	47 nF [C1210C473K5HACT U]

Multisim 14.1 Base Edition Components

47 nF [C1210C473K5RACT U]	47 nF [C2220C473K2GACT U]	47 nF [MDC10473K100A5 2P3TUBE]	47 nF [MDK10473K250A5 2P3TUBE]
47 nF [C1210C473KARACT U]	47 nF [C2220C473K5GACT U]	47 nF [MDC10473K250A5 2P3TUBE]	47 nF [MDK10473K400A5 2P3TUBE]
47 nF [C1812C473K1GACT U]	47 nF [CA064C473K4RACT U]	47 nF [MDC10473K400A5 2P3TUBE]	47 nF [MDK10473K50A52 P3TUBE]
47 nF [C1812C473K1HACT U]	47 nF [CA064C473K8RACT U]	47 nF [MDC10473K50A52 P3TUBE]	47 nF [MDS10473K100A5 2P3TUBE]
47 nF [C1812C473K1RACT U]	47 nF [GMC5.7472K250J3 1TR12]	47 nF [MDC10473K630A5 2P3TUBE]	47 nF [MDS10473K250A5 2P3TUBE]
47 nF [C1812C473K2RACT U]	47 nF [GMC5.7473K50J31 TR12]	47 nF [MDC15473K100B5 3P3TUBE]	47 nF [MDS10473K400A5 2P3TUBE]
47 nF [C1812C473K5GACT U]	47 nF [GMC7.3472K250K3 1TR12]	47 nF [MDC15473K250B5 3P3TUBE]	47 nF [MDS10473K50A52 P3TUBE]
47 nF [C1812C473K5HACT U]	47 nF [GMC7.3472K63K31 TR12]	47 nF [MDC15473K400B5 3P3TUBE]	47 nF [MDS10473K630A5 2P3TUBE]
47 nF [C1812C473K5RACT U]	47 nF [GMC7.3473K63K31 TR12]	47 nF [MDC15473K50B53 P3TUBE]	47 nF [MDS15473K100B5 3P3TUBE]
47 nF [C1825C473K5RACT U]	47 nF [GPC7.3473K63K33 TR12]	47 nF [MDC15473K630B5 3P3TUBE]	47 nF [MDS15473K250B5 3P3TUBE]
47 nF [C2220C473K1GACT U]	47 nF [LG126Z473MAT2S 1]	47 nF [MDK10473K100A5 2P3TUBE]	47 nF [MMC7.3473K100K 31TR12]

Multisim 14.1 Base Edition Components

47 nF [MMC7.3473K50K3 1TR12]	47 nF [PG226W473MAB2 S1]	47 Ohm [4114R-2- 470]	47 Ohm [4308R- 102-470LF]
47 nF [PG124D473MAB2S 1]	47 nF [PG226Z473MAB2S 1]	47 Ohm [4114R-2- 470LF]	47 Ohm [4310H- 101-470]
47 nF [PG124W473MAB2 S1]	47 nF [SPC10.2473K100A 31TR16]	47 Ohm [4116R-1- 470]	47 Ohm [4310H- 101-470LF]
47 nF [PG124Z473MAB2S 1]	47 nF [SPC10.2473K250A 31TR16]	47 Ohm [4116R-1- 470LF]	47 Ohm [4310M- 101-470]
47 nF [PG126D473MAB2S 1]	47 nF [SPC12.7473K400B 31TR24]	47 Ohm [4116R-2- 470]	47 Ohm [4310M- 101-470LF]
47 nF [PG126W473MAB2 S1]	47 nF [SPC16.5473K630C 31TR24]	47 Ohm [4116R-2- 470LF]	47 Ohm [4310M- 102-470]
47 nF [PG126Z473MAB2S 1]	47 nF [W2L13C473MAT1S]	47 Ohm [4306R- 101-470]	47 Ohm [4310M- 102-470LF]
47 nF [PG224D473MAB2S 1]	47 nF [W2L1YC473MAT1A]	47 Ohm [4306R- 102-470]	47 Ohm [4310R- 101-470]
47 nF [PG224W473MAB2 S1]	47 nF [W3F15C4738AT1A]	47 Ohm [4306R- 102-470LF]	47 Ohm [4310R- 102-470]
47 nF [PG224Z473MAB2S 1]	47 nF [W3L1YC473MAT1A]	47 Ohm [4306R- 102-470LF]	47 Ohm [4310R- 102-470LF]
47 nF [PG226D473MAB2S 1]	47 Ohm [4114R-1- 470]	47 Ohm [4308H- 102-470LF]	47 Ohm [4310R- 102-470LF]
	47 Ohm [4114R-1- 470LF]	47 Ohm [4308H- 102-470]	47 Ohm [4311R- 101-470]
		47 Ohm [4308R- 101-470]	47 Ohm [4416P-1- 470]
		47 Ohm [4308R- 101-470LF]	47 Ohm [4416P-1- 470LF]
		47 Ohm [4308R- 102-470]	47 Ohm [4416P- T01-470]

Multisim 14.1 Base Edition Components

47 Ohm [4420P-1-470]	47 Ohm [4610H-102-470LF]	47 Ohm [4816P-1-470LF]	47 Ohm [CAT25-470JALF]
47 Ohm [4420P-T01-470]	47 Ohm [4610X-101-470LF]	47 Ohm [4816P-2-470]	47 Ohm [CAY10-470J2LF]
47 Ohm [4420P-T02-470]	47 Ohm [4610X-102-470LF]	47 Ohm [4816P-2-470LF]	47 Ohm [CAY10-470J4LF]
47 Ohm [4604X-102-470LF]	47 Ohm [4610X-AP1-470LF]	47 Ohm [4816P-T01-470]	47 Ohm [CAY16-470J2LF]
47 Ohm [4605X-101-470LF]	47 Ohm [4612X-102-470LF]	47 Ohm [4816P-T01-470LF]	47 Ohm [CAY16-470J4LF]
47 Ohm [4606H-102-470LF]	47 Ohm [4613X-101-470LF]	47 Ohm [4816P-T02-470]	47 Ohm [CAY16-470J8LF]
47 Ohm [4606X-101-470LF]	47 Ohm [4614X-102-470LF]	47 Ohm [4816P-T02-470LF]	47 Ohm [CAY16-47R0F4LF]
47 Ohm [4606X-102-470LF]	47 Ohm [4814P-1-470]	47 Ohm [4820P-1-470]	47 Ohm [CAY17-470JALF]
47 Ohm [4607X-101-470LF]	47 Ohm [4814P-1-470LF]	47 Ohm [4820P-T01-470]	47 Ohm [CR0201-FW-47R0GLF]
47 Ohm [4608H-102-470LF]	47 Ohm [4814P-2-470]	47 Ohm [CAT10-470J4LF]	47 Ohm [CR0402-FX-47R0GLF]
47 Ohm [4608M-102-470LF]	47 Ohm [4814P-2-470LF]	47 Ohm [CAT16-470J2LF]	47 Ohm [CR0402-JW-470GLF]
47 Ohm [4608X-101-470LF]	47 Ohm [4814P-T01-470]	47 Ohm [CAT16-470J4LF]	47 Ohm [CR0603-FX-47R0ELF]
47 Ohm [4608X-102-470LF]	47 Ohm [4814P-T01-470LF]	47 Ohm [CAT16-470J8LF]	47 Ohm [CR0603-FX-47R0HLF]
47 Ohm [4608X-AP2-470LF]	47 Ohm [4814P-T02-470]	47 Ohm [CAT16-47R0F4LF]	47 Ohm [CR0603-JW-470ELF]
47 Ohm [4609X-101-470LF]	47 Ohm [4816P-1-470]	47 Ohm [CAT16-47R0F8LF]	47 Ohm [CR0603-JW-470GLF]

Multisim 14.1 Base Edition Components

47 Ohm [CR0805-FX-47R0ELF]	47 Ohm [CRT0805-BY-47R0ELF]	47 Ohm [PWR220T-20-47R0F]	47 Ohm [PWR263S-20-47R0JE]
47 Ohm [CR0805-FX-47R0GLF]	47 Ohm [CRT0805-CV-47R0ELF]	47 Ohm [PWR220T-20-47R0J]	47 Ohm [PWR263S-35-47R0F]
47 Ohm [CR0805-JW-470ELF]	47 Ohm [CRT1206-CW-47R0ELF]	47 Ohm [PWR220T-35-47R0F]	47 Ohm [PWR263S-35-47R0FE]
47 Ohm [CR1206-FX-47R0ELF]	47 Ohm [FW10A47R0JA]	47 Ohm [PWR220T-35-47R0J]	47 Ohm [PWR263S-35-47R0J]
47 Ohm [CR1206-JW-470ELF]	47 Ohm [FW20A47R0JA]	47 Ohm [PWR221T-30-47R0F]	47 Ohm [PWR263S-35-47R0JE]
47 Ohm [CR2010-FX-47R0ELF]	47 Ohm [FW30A47R0JA]	47 Ohm [PWR221T-30-47R0J]	47 Ohm [PWR3014W47R0FE]
47 Ohm [CR2512-JW-470ELF]	47 Ohm [FW50A47R0JA]	47 Ohm [PWR2615W47R0F]	47 Ohm [PWR3014W47R0JE]
47 Ohm [CRM1206-FX-47R0ELF]	47 Ohm [FW70A47R0JA]	47 Ohm [PWR2615W47R0J]	47 Ohm [PWR4318W47R0JE]
47 Ohm [CRM1206-JW-470ELF]	47 Ohm [PWR163S-25-47R0F]	47 Ohm [PWR2615W47R0JE]	47 Ohm [PWR4525W47R0J]
47 Ohm [CRM2512-JW-470ELF]	47 Ohm [PWR163S-25-47R0FE]	47 Ohm [PWR263S-20-47R0F]	47 Ohm [PWR4525W47R0JE]
47 Ohm [CRS2010-FX-47R0ELF]	47 Ohm [PWR163S-25-47R0J]	47 Ohm [PWR263S-20-47R0FE]	47 Ohm [PWR5322W47R0JE]
47 Ohm [CRS2512-FX-47R0ELF]	47 Ohm [PWR163S-25-47R0JE]	47 Ohm [PWR263S-20-47R0J]	47 Ohm [PWR6327W47R0J]
47 Ohm [CRT0603-FY-47R0ELF]	47 Ohm [PWR2010W47R0JE]		
47 Ohm [CRT0805-BW-47R0ELF]			

Multisim 14.1 Base Edition Components

47 Ohm [PWR6327W47R0JE]	47 pF [C0805C470K2GACT U]	47 pF [C1206C470KFGACT U]	47 pF [CA064C470K8GAC TU]
47 Ohm [WS1A47R0J]	47 pF [C0805C470K3GACT U]	47 pF [C1206C470KGGAC TU]	47 pF [W2F11A4708AT1A]
47 Ohm [WS2M47R0J]	47 pF [C0805C470K5GACT U]	47 pF [C1210C470K5GACT U]	47 pF [W3F11A4708AT1A]
47 pF [C0201C470K3GACT U]	47 pF [C0805C470KBGAC TU]	47 pF [C1210C470KBGAC TU]	47 uF [10TPB47M]
47 pF [C0402C470K3GACT U]	47 pF [C0805C470KCGAC TU]	47 pF [C1812C470KBGAC TU]	47 uF [10TPE47MAZB]
47 pF [C0402C470K4GACT U]	47 pF [C1206C470K1GACT U]	47 pF [C1812C470KDGAC TU]	47 uF [10TPG47M]
47 pF [C0402C470K5GACT U]	47 pF [C1206C470K2GACT U]	47 pF [C1825C470KBGAC TU]	47 uF [16TQC47MW]
47 pF [C0402C470K8GACT U]	47 pF [C1206C470K3GACT U]	47 pF [C2220C470KBGAC TU]	47 uF [16TQC47MYFD]
47 pF [C0603C470K1GACT U]	47 pF [C1206C470K5GACT U]	47 pF [C2225C470KBGAC TU]	47 uF [16TQC47MYFT]
47 pF [C0603C470K5GACT U]	47 pF [C1206C470KBGAC TU]	47 pF [CA064C470K3GAC TU]	47 uF [20SVP47M]
47 pF [C0603C470K8GACT U]	47 pF [C1206C470KDGAC TU]	47 pF [CA064C470K5GAC TU]	47 uF [20TQC47MYF]
47 pF [C0805C470K1GACT U]			47 uF [20TQC47MYFT]
			47 uF [2R5TPU47MSI]
			47 uF [6TPC47M]
			47 uF [6TPC47MB]
			47 uF [6TPH47MHA]

Multisim 14.1 Base Edition Components

47 uF [6TPU47MSI]	47 uF [EEHZC1V470P]	47 uF [T491D476M010AT]	47 uF [T491X476M035AT]
47 uF [8TPG47M]	47 uF [T409H476M010AH 4250]	47 uF [T491D476M016AT]	47 uF [T494A476M004AT]
47 uF [A700V476M006AT E018]	47 uF [T419F476M010AH 4250]	47 uF [T491D476M020AT]	47 uF [T494A476M006AT]
47 uF [A700V476M006AT E025]	47 uF [T491A476M004AT]	47 uF [T491D476M025AT]	47 uF [T494B476M004AT]
47 uF [A700V476M006AT E028]	47 uF [T491A476M006AT]	47 uF [T491E476M035AT]	47 uF [T494B476M006AT]
47 uF [EEFCS1A470R]	47 uF [T491B476M004AT]	47 uF [T491T476M004AT]	47 uF [T494B476M010AT]
47 uF [EEFCT1C470R]	47 uF [T491B476M006AT]	47 uF [T491T476M006AT]	47 uF [T494C476M004AT]
47 uF [EEFCT1D470R]	47 uF [T491B476M010AT]	47 uF [T491U476M004AT]	47 uF [T494C476M006AT]
47 uF [EEFCX1A470R]	47 uF [T491C476M004AT]	47 uF [T491U476M006AT]	47 uF [T494C476M010AT]
47 uF [EEFCX1C470R]	47 uF [T491C476M006AT]	47 uF [T491U476M010AT]	47 uF [T494C476M016AT]
47 uF [EEFCX1D470R]	47 uF [T491C476M010AT]	47 uF [T491V476M010AT]	47 uF [T494D476M006AT]
47 uF [EEFHX1A470R]	47 uF [T491C476M016AT]	47 uF [T491V476M016AT]	47 uF [T494D476M010AT]
47 uF [EEFHX1C470R]	47 uF [T491D476M006AT]	47 uF [T491X476M025AT]	47 uF [T494D476M016AT]
47 uF [EEFHX1D470R]			
47 uF [EEHZA1V470P]			

Multisim 14.1 Base Edition Components

47 uF [T494D476M020AT]	47 uF [T495B476M010AT E500]	47 uF [T495D476M025AT E250]	47 uF [T495X476M035AT E300]
47 uF [T494D476M025AT]	47 uF [T495C476M016AT E350]	47 uF [T495V476M006AT E150]	47 uF [T497G476M006AT 6110]
47 uF [T494E476M035AT]	47 uF [T495D476M010AT E080]	47 uF [T495X476M020AT E065]	47 uF [T498C476M006AT E800]
47 uF [T494T476M004AT]	47 uF [T495D476M010AT E090]	47 uF [T495X476M020AT E100]	47 uF [T498D476M010AT E600]
47 uF [T494T476M006AT]	47 uF [T495D476M010AT E200]	47 uF [T495X476M020AT E150]	47 uF [T498D476M016AT E600]
47 uF [T494U476M004AT]	47 uF [T495D476M016AT E080]	47 uF [T495X476M025AT E080]	47 uF [T510E476M035AT E050]
47 uF [T494U476M010AT]	47 uF [T495D476M016AT E100]	47 uF [T495X476M025AT E150]	47 uF [T510X476M035AT E055]
47 uF [T494V476M010AT]	47 uF [T495D476M016AT E150]	47 uF [T495X476M025AT E185]	47 uF [T510X476M035AT E065]
47 uF [T494V476M016AT]	47 uF [T495D476M020AT E100]	47 uF [T495X476M025AT E200]	47 uF [T520A476M004AT E070]
47 uF [T494X476M025AT]	47 uF [T495D476M020AT E175]	47 uF [T495X476M035AT E185]	47 uF [T520A476M004AT E080]
47 uF [T494X476M035AT]	47 uF [T495D476M025AT E120]	47 uF [T495X476M035AT E200]	47 uF [T520A476M006AT E150]

Multisim 14.1 Base Edition Components

47 uF [T520A476M2R5AT E090]	47 uF [T520D476M016AT E070]	47 uF [T521X476M035AT E030]	47 uF [TAJA476K004RNJ]
47 uF [T520B476M006AT E025]	47 uF [T520Q476M011AT E040]	47 uF [T521X476M035AT E070]	47 uF [TAJA476K006RNJ]
47 uF [T520B476M006AT E035]	47 uF [T520T476M004AT E070]	47 uF [T525B476M006AT E080]	47 uF [TAJB476K004RNJ]
47 uF [T520B476M006AT E040]	47 uF [T520T476M006AT E040]	47 uF [T525D476M016AT E035]	47 uF [TAJB476K010RNJ]
47 uF [T520B476M006AT E070]	47 uF [T520T476M006AT E070]	47 uF [T525D476M016AT E065]	47 uF [TAJC476K006RNJ]
47 uF [T520B476M008AT E035]	47 uF [T520V476M016AT E045]	47 uF [T525T476M006AT E080]	47 uF [TAJC476K016RNJ]
47 uF [T520B476M008AT E070]	47 uF [T520V476M016AT E070]	47 uF [T543A476M004AT E080]	47 uF [TAJC476K020RNJ]
47 uF [T520B476M010AT E035]	47 uF [T520W476M016AT E045]	47 uF [T543W476M016AT E045]	47 uF [TAJD476K010RNJ]
47 uF [T520B476M010AT E070]	47 uF [T521D476M020AT E055]	47 uF [TACR476K002RTA]	47 uF [TAJD476K020RNJ]
47 uF [T520C476M010AT E100]	47 uF [T521V476M020AT E090]	47 uF [TACR476K003RTA]	47 uF [TAJD476K025RNJ]
47 uF [T520D476M016AT E035]	47 uF [T521W476M020AT E045]	47 uF [TACR476K004RTA]	47 uF [TAJE476K020RNJ]
		47 uF [TAJA476K002RNJ]	47 uF [TAJE476K025RNJ]

Multisim 14.1 Base Edition Components

47 uF [TAJE476K035RNJ]	47 uF [THJD476K016RJN]	47 uF [TPSC476K006R030 0]	47 uF [TPSD476K025R015 0]
47 uF [TAJT476K006RNJ]	47 uF [TPMD476K020R00 45]	47 uF [TPSC476K010R035 0]	47 uF [TPSD476K025R025 0]
47 uF [TAJV476K035RNJ]	47 uF [TPMD476K020R00 55]	47 uF [TPSC476K016R011 0]	47 uF [TPSE476K020R007 0]
47 uF [TAJW476K010RNJ]	47 uF [TPME476K035R00 65]	47 uF [TPSC476K016R035 0]	47 uF [TPSE476K020R012 5]
47 uF [TAJW476K016RNJ]	47 uF [TPSA476K004R050 0]	47 uF [TPSD476K010R010 0]	47 uF [TPSE476K020R015 0]
47 uF [TAJX476K016RNJ]	47 uF [TPSB476K006R025 0]	47 uF [TPSD476K016R008 0]	47 uF [TPSE476K020R020 0]
47 uF [TAJY476K010RNJ]	47 uF [TPSB476K006R035 0]	47 uF [TPSD476K016R010 0]	47 uF [TPSE476K020R025 0]
47 uF [TAJY476K016RNJ]	47 uF [TPSB476K006R050 0]	47 uF [TPSD476K016R015 0]	47 uF [TPSE476K025R008 0]
47 uF [TAJY476K020RNJ]	47 uF [TPSB476K010R035 0]	47 uF [TPSD476K016R020 0]	47 uF [TPSE476K025R010 0]
47 uF [THJC476K006RJN]	47 uF [TPSB476K010R050 0]	47 uF [TPSD476K020R010 0]	47 uF [TPSE476K025R012 5]
47 uF [THJC476K010RJN]	47 uF [TPSB476K010R065 0]	47 uF [TPSD476K020R020 0]	47 uF [TPSE476K035R020 0]

Multisim 14.1 Base Edition Components

47 uF [TPSE476K035R025 0]	47 uH [SDE0805A- 470K]	47 uH [SDR1305- 470M]	47 uH [SRN8040- 470M]
47 uF [TPSW476K010R01 25]	47 uH [SDE1006A- 470K]	47 uH [SDR1307- 470KL]	47 uH [SRP1038A- 470M]
47 uF [TPSW476K010R01 50]	47 uH [SDR0302- 470KL]	47 uH [SDR1307A- 470K]	47 uH [SRP1265A- 470M]
47 uF [TPSW476K010R01 50]	47 uH [SDR0403- 470KL]	47 uH [SDR1806- 470ML]	47 uH [SRP1770TA- 470M]
47 uF [TPSW476K010R02 50]	47 uH [SDR0503- 470KL]	47 uH [SDR6603- 470M]	47 uH [SRP6540- 470M]
47 uF [TPSY476K016R025 0]	47 uH [SDR0603- 470KL]	47 uH [SDR7030- 470K]	47 uH [SRP7050TA- 470M]
47 uF [TRJC476K010RRJ]	47 uH [SDR0604- 470KL]	47 uH [SDR7045- 470K]	47 uH [SRR0603- 470KL]
47 uF [TRJC476K016RRJ]	47 uH [SDR0703- 470KL]	47 uH [SRN1060- 470M]	47 uH [SRR0604- 470KL]
47 uF [TRJD476K020RRJ]	47 uH [SDR0805- 470KL]	47 uH [SRN3010- 470M]	47 uH [SRR0618- 470ML]
47 uF [TRJD476K025RRJ]	47 uH [SDR0906- 470KL]	47 uH [SRN3015- 470M]	47 uH [SRR0735A- 470M]
47 uF [TRMD476K020R00 55]	47 uH [SDR1005- 470KL]	47 uH [SRN4018- 470M]	47 uH [SRR0745A- 470M]
47 uF [TRME476K025R00 65]	47 uH [SDR1006- 470KL]	47 uH [SRN4026- 470M]	47 uH [SRR0804- 470K]
47 uH [SDE0403A- 470K]	47 uH [SDR1030- 470M]	47 uH [SRN5040- 470M]	47 uH [SRR0805- 470Y]
47 uH [SDE0604A- 470M]	47 uH [SDR1045- 470M]	47 uH [SRN6028- 470M]	47 uH [SRR0905- 470Y]
	47 uH [SDR1105- 470KL]	47 uH [SRN6045- 470M]	47 uH [SRR0906- 470ML]

Multisim 14.1 Base Edition Components

47 uH [SRR0908-470ML]	47 uH [SRR4028-470Y]	47 uH [SRU1063-470Y]	47 uH [SRU8028A-470Y]
47 uH [SRR1003-470M]	47 uH [SRR5018-470Y]	47 uH [SRU2013-470Y]	47 uH [SRU8043-470Y]
47 uH [SRR1005-470Y]	47 uH [SRR5028-470Y]	47 uH [SRU2016-470Y]	47.5 kOhm [CAY16-4752F4LF]
47 uH [SRR1206-470YL]	47 uH [SRR6028-470Y]	47 uH [SRU3017-470Y]	47.5 kOhm [CR0402-FX-4752GLF]
47 uH [SRR1208-470YL]	47 uH [SRR6038-470Y]	47 uH [SRU3028-470Y]	47.5 kOhm [CR0603-FX-4752ELF]
47 uH [SRR1210-470M]	47 uH [SRR6040A-470M]	47 uH [SRU5011-470Y]	47.5 kOhm [CR0805-FX-4752ELF]
47 uH [SRR1210A-470M]	47 uH [SRR6603-470ML]	47 uH [SRU5016-470Y]	47.5 kOhm [CR1206-FX-4752ELF]
47 uH [SRR1240-470M]	47 uH [SRR7032-470M]	47 uH [SRU5018-470Y]	47.5 kOhm [CR2512-FX-4752ELF]
47 uH [SRR1260-470M]	47 uH [SRR7045-470M]	47 uH [SRU5028-470Y]	47.5 kOhm [CRT0603-BY-4752ELF]
47 uH [SRR1260A-470M]	47 uH [SRU1028-470Y]	47 uH [SRU5028A-470Y]	47.5 kOhm [CRT0805-FX-4752ELF]
47 uH [SRR1280-470M]	47 uH [SRU1028A-470Y]	47 uH [SRU6011-470Y]	47.5 Ohm [CAT16-47R5F4LF]
47 uH [SRR1806-470M]	47 uH [SRU1038-470Y]	47 uH [SRU6018-470Y]	47.5 Ohm [CAY16-47R5F4LF]
47 uH [SRR3011-470YL]	47 uH [SRU1038A-470Y]	47 uH [SRU6025-470Y]	47.5 Ohm [CR0402-FX-47R5GLF]
47 uH [SRR4011-470YL]	47 uH [SRU1048-470Y]	47 uH [SRU6025A-470Y]	
47 uH [SRR4018-470Y]	47 uH [SRU1048A-470Y]	47 uH [SRU8028-470Y]	

Multisim 14.1 Base Edition Components

47.5 Ohm [CR0603-FX-47R5ELF]	470 kOhm [4306R-102-474]	470 kOhm [4606X-101-474LF]	470 kOhm [4816P-T01-474]
47.5 Ohm [CR0805-FX-47R5ELF]	470 kOhm [4306R-102-474LF]	470 kOhm [4606X-102-474LF]	470 kOhm [4816P-T01-474LF]
47.5 Ohm [CR1206-FX-47R5ELF]	470 kOhm [4308R-101-474]	470 kOhm [4607X-101-474LF]	470 kOhm [4816P-T02-474]
47.5 Ohm [CRM1206-FX-47R5ELF]	470 kOhm [4308R-101-474LF]	470 kOhm [4608H-102-474LF]	470 kOhm [4816P-T02-474LF]
47.5 Ohm [CRT0603-FZ-47R5ELF]	470 kOhm [4308R-102-474]	470 kOhm [4608M-101-474LF]	470 kOhm [4820P-T01-474]
470 kOhm [4114R-1-474]	470 kOhm [4308R-102-474LF]	470 kOhm [4608X-101-474LF]	470 kOhm [CAT16-4703F4LF]
470 kOhm [4114R-1-474LF]	470 kOhm [4309R-101-474]	470 kOhm [4608X-102-474LF]	470 kOhm [CAT16-474J4LF]
470 kOhm [4114R-2-474]	470 kOhm [4309R-101-474LF]	470 kOhm [4608X-AP2-474LF]	470 kOhm [CAT25-474JALF]
470 kOhm [4116R-1-474]	470 kOhm [4310R-101-474]	470 kOhm [4609X-101-474LF]	470 kOhm [CAY10-474J4LF]
470 kOhm [4116R-1-474LF]	470 kOhm [4310R-101-474LF]	470 kOhm [4610X-101-474LF]	470 kOhm [CAY16-4703F4LF]
470 kOhm [4116R-1-474LF]	470 kOhm [4310R-102-474]	470 kOhm [4610X-102-474LF]	470 kOhm [CAY16-474J2LF]
470 kOhm [4116R-2-474]	470 kOhm [4310R-102-474LF]	470 kOhm [4816P-1-474]	470 kOhm [CAY16-474J4LF]
470 kOhm [4116R-2-474LF]	470 kOhm [4604X-101-474LF]	470 kOhm [4816P-1-474LF]	470 kOhm [CAY16-474J8LF]
470 kOhm [4306M-102-474LF]	470 kOhm [4604X-102-474LF]	470 kOhm [4816P-2-474]	470 kOhm [CHV0805-JW-474ELF]
470 kOhm [4306R-101-474]	470 kOhm [4605X-101-474LF]	470 kOhm [4816P-2-474LF]	470 kOhm [CHV2010-FW-4703ELF]
470 kOhm [4306R-101-474LF]			

Multisim 14.1 Base Edition Components

470 kOhm [CR0201-JW-474GLF]	470 kOhm [CRM1206-FX-4703ELF]	470 mOhm [CRL2010-JW-R470ELF]	470 mOhm [PWR4525WR470J]
470 kOhm [CR0402-FX-4703GLF]	470 kOhm [CRM1206-JW-474ELF]	470 mOhm [CRL2512-FW-R470ELF]	470 mOhm [PWR4525WR470JE]
470 kOhm [CR0402-JW-474GLF]	470 kOhm [CRM2010-JW-474ELF]	470 mOhm [CRL2512-JW-R470ELF]	470 mOhm [PWR6327WR470J]
470 kOhm [CR0603-FX-4703ELF]	470 kOhm [CRT0805-CX-4703ELF]	470 mOhm [CRM1206-FX-R470ELF]	470 mOhm [PWR6327WR470JE]
470 kOhm [CR0603-JW-474ELF]	470 mOhm [CRL0603-FW-R470ELF]	470 mOhm [CRM2010-FX-R470ELF]	470 nF [05086C474KAT2V]
470 kOhm [CR0805-FX-4703ELF]	470 mOhm [CRL0603-JW-R470ELF]	470 mOhm [CRM2512-FX-R470ELF]	470 nF [0508ZC474KAT2V]
470 kOhm [CR0805-JW-474ELF]	470 mOhm [CRL0805-FW-R470ELF]	470 mOhm [CRM2512-JX-R470ELF]	470 nF [0612YC474KAT2V]
470 kOhm [CR0805-JW-474GLF]	470 mOhm [CRL0805-JW-R470ELF]	470 mOhm [PWR1913WR470J]	470 nF [0612ZC474KAT2S]
470 kOhm [CR1206-FX-4703ELF]	470 mOhm [CRL1206-FW-R470ELF]	470 mOhm [PWR1913WR470JE]	470 nF [C0603C474K4PACT U]
470 kOhm [CR1206-FX-4703GLF]	470 mOhm [CRL1206-JW-R470ELF]	470 mOhm [PWR2615WR470J]	470 nF [C0603C474K8PACT U]
470 kOhm [CR1206-JW-474ELF]	470 mOhm [CRL2010-FW-R470ELF]	470 mOhm [PWR4318WR470JE]	470 nF [C0603C474K8RACT U]

Multisim 14.1 Base Edition Components

470 nF [C0603C474K9PACT U]	470 nF [C1206C474K4RACT U]	470 nF [C1210C474M5UAC TU]	470 nF [C1825C474K1RACT U]
470 nF [C0603C474K9RACT U]	470 nF [C1206C474K5NAC TU]	470 nF [C1210F474K1RACT U]	470 nF [C1825C474K5RACT U]
470 nF [C0805C474K3NAC TU]	470 nF [C1206C474K5RACT U]	470 nF [C1210F474K3RACT U]	470 nF [C1825C474KARACT U]
470 nF [C0805C474K3PACT U]	470 nF [C1206C474K8RACT U]	470 nF [C1210F474K4RACT U]	470 nF [C2220C474K1RACT U]
470 nF [C0805C474K3RACT U]	470 nF [C1206C474M3VAC TU]	470 nF [C1210F474K5RACT U]	470 nF [C2220C474K5RACT U]
470 nF [C0805C474K4RACT U]	470 nF [C1206C474M4VAC TU]	470 nF [C1812C474K5RACT U]	470 nF [C2220C474KARACT U]
470 nF [C0805C474K8RACT U]	470 nF [C1206F474K3RACT U]	470 nF [C1812C474KARACT U]	470 nF [C2225C474K1RACT U]
470 nF [C0805C474M3VAC TU]	470 nF [C1206F474K4RACT U]	470 nF [C1812C474M5UAC TU]	470 nF [C2225C474K2RACT U]
470 nF [C0805C474M4VAC TU]	470 nF [C1210C474K3RACT U]	470 nF [C1812F474K1RACT U]	470 nF [C2225C474K5RACT U]
470 nF [C1206C474K3NAC TU]	470 nF [C1210C474K4RACT U]	470 nF [C1812F474K3RACT U]	470 nF [C2225C474KARACT U]
470 nF [C1206C474K3RACT U]	470 nF [C1210C474K5RACT U]	470 nF [C1812F474K5RACT U]	470 nF [C2225C474M1UAC TU]

Multisim 14.1 Base Edition Components

470 nF [CDR06BX474AKSM]	470 nF [MDK10474K250A5 2P3TUBE]	470 nF [T491A474M025AT]	470 nF [TAJB474K035RNJ]
470 nF [LDECD3470KA5N0 0]	470 nF [MDK10474K50A52 P3TUBE]	470 nF [T491A474M035AT]	470 nF [TAJB474K050RNJ]
470 nF [LG224Z474MAT2S 1]	470 nF [MDS10474K100A5 2P3TUBE]	470 nF [T491B474M035AT]	470 nF [TAJC474K050RNJ]
470 nF [MDC10474K100A5 2P3TUBE]	470 nF [MDS10474K250A5 2P3TUBE]	470 nF [T491C474M050AT]	470 nF [TAJR474K025RNJ]
470 nF [MDC10474K250A5 2P3TUBE]	470 nF [MDS10474K50A52 P3TUBE]	470 nF [T494A474M025AT]	470 nF [TAJR474K035RNJ]
470 nF [MDC10474K400A5 8P7TUBE]	470 nF [MDS15474K100B5 3P3TUBE]	470 nF [T494B474M035AT]	470 nF [TAJS474K025RNJ]
470 nF [MDC10474K400A5 8P8TUBE]	470 nF [MDS15474K250B5 3P3TUBE]	470 nF [T494B474M050AT]	470 nF [TAJS474K035RNJ]
470 nF [MDC10474K50A52 P3TUBE]	470 nF [PG224D474MAB2S 1]	470 nF [T494C474M050AT]	470 nF [TAJT474K035RNJ]
470 nF [MDC15474K100B5 3P3TUBE]	470 nF [PG224W474MAB2 S1]	470 nF [T498A474M025AT E8K5]	470 nF [THJA474K025RJN]
470 nF [MDC15474K250B5 3P3TUBE]	470 nF [PG224Z474MAB2S 1]	470 nF [TAJA474K025RNJ]	470 nF [THJB474K035RJN]
470 nF [MDC15474K50B53 P3TUBE]	470 nF [SPC16.5474K100C 31TR24]	470 nF [TAJA474K035RNJ]	470 nF [TPSA474K025R700 0]
		470 nF [TAJA474K050RNJ]	

Multisim 14.1 Base Edition Components

470 nF [TPSB474K035R400 0]	470 nH [SRP1245A- R47M]	470 Ohm [4114R-1- 471]	470 Ohm [4306R- 101-471LF]
470 nF [TPSC474K050R230 0]	470 nH [SRP1250- R47M]	470 Ohm [4114R-1- 471LF]	470 Ohm [4306R- 102-471]
470 nF [W2L1ZC474MAT1A]	470 nH [SRP1265A- R47M]	470 Ohm [4114R-2- 471]	470 Ohm [4306R- 102-471LF]
470 nF [W2L1ZC474MAT1S]	470 nH [SRP1270- R47M]	470 Ohm [4114R-2- 471LF]	470 Ohm [4308H- 101-471]
470 nF [W2L1ZC474MAT1S]	470 nH [SRP4012- R47M]	470 Ohm [4116R-1- 471]	470 Ohm [4308H- 101-471LF]
470 nF [W3L1YC474MAT1A]	470 nH [SRP4012TA-R47M]	470 Ohm [4116R-1- 471LF]	470 Ohm [4308H- 102-471]
470 nF [W3L1ZC474MAT1S]	470 nH [SRP4020- R47M]	470 Ohm [4116R-2- 471]	470 Ohm [4308H- 102-471LF]
470 nF [W3L1ZC474MAT1S]	470 nH [SRP4020TA-R47M]	470 Ohm [4116R-2- 471LF]	470 Ohm [4308M- 101-471]
470 nH [SRN2010- R47M]	470 nH [SRP5015TA-R47M]	470 Ohm [4304M- 102-471]	470 Ohm [4308M- 102-471]
470 nH [SRN2012- R47M]	470 nH [SRP5030TA-R47M]	470 Ohm [4304M- 102-471LF]	470 Ohm [4308M- 102-471LF]
470 nH [SRN2510- R47M]	470 nH [SRP5030T- R47M]	470 Ohm [4306H- 101-471]	470 Ohm [4308R- 101-471]
470 nH [SRN2512- R47M]	470 nH [SRP7028A- R47M]	470 Ohm [4306H- 101-471LF]	470 Ohm [4308R- 101-471LF]
470 nH [SRN4012T- R47M]	470 nH [SRP7030- R47FM]	470 Ohm [4306H- 102-471]	470 Ohm [4308R- 102-471]
470 nH [SRP1040- R47M]	470 nH [SRP7050TA-R47M]	470 Ohm [4306H- 102-471LF]	470 Ohm [4308R- 102-471LF]
470 nH [SRP1235- R47M]	470 nH [SRR4011- R47YL]	470 Ohm [4306R- 101-471]	470 Ohm [4309R- 101-471]

Multisim 14.1 Base Edition Components

470 Ohm [4309R-101-471LF]	470 Ohm [4416P-2-471]	470 Ohm [4606X-101-471LF]	470 Ohm [4609X-101-471LF]
470 Ohm [4310H-101-471]	470 Ohm [4416P-T01-471]	470 Ohm [4606X-102-471LF]	470 Ohm [4609X-AP1-471LF]
470 Ohm [4310H-101-471LF]	470 Ohm [4416P-T02-471]	470 Ohm [4606X-AP1-471LF]	470 Ohm [4610H-101-471LF]
470 Ohm [4310H-102-471]	470 Ohm [4420P-1-471]	470 Ohm [4606X-AP2-471LF]	470 Ohm [4610H-102-471LF]
470 Ohm [4310H-102-471LF]	470 Ohm [4420P-2-471]	470 Ohm [4607X-101-471LF]	470 Ohm [4610M-101-471LF]
470 Ohm [4310M-101-471]	470 Ohm [4420P-T01-471]	470 Ohm [4608H-101-471LF]	470 Ohm [4610X-101-471LF]
470 Ohm [4310M-101-471LF]	470 Ohm [4420P-T02-471]	470 Ohm [4608H-102-471LF]	470 Ohm [4610X-102-471LF]
470 Ohm [4310M-102-471]	470 Ohm [4604X-101-471LF]	470 Ohm [4608M-101-471LF]	470 Ohm [4610X-AP1-471LF]
470 Ohm [4310M-102-471LF]	470 Ohm [4604X-102-471LF]	470 Ohm [4608M-102-471LF]	470 Ohm [4611X-101-471LF]
470 Ohm [4310R-101-471]	470 Ohm [4605H-101-471LF]	470 Ohm [4608X-101-471LF]	470 Ohm [4612H-101-471LF]
470 Ohm [4310R-101-471LF]	470 Ohm [4605M-101-471LF]	470 Ohm [4608X-102-471LF]	470 Ohm [4612M-101-471LF]
470 Ohm [4310R-102-471]	470 Ohm [4605X-101-471LF]	470 Ohm [4608X-AP1-471LF]	470 Ohm [4612X-101-471LF]
470 Ohm [4310R-102-471LF]	470 Ohm [4605X-AP1-471LF]	470 Ohm [4608X-AP2-471LF]	470 Ohm [4612X-102-471LF]
470 Ohm [4416P-1-471]	470 Ohm [4606M-101-471LF]	470 Ohm [4609H-101-471LF]	470 Ohm [4614X-102-471LF]
470 Ohm [4416P-1-471LF]	470 Ohm [4606M-102-471LF]	470 Ohm [4609M-101-471LF]	470 Ohm [4814P-1-471]

Multisim 14.1 Base Edition Components

470 Ohm [4814P-1-471LF]	470 Ohm [4816P-T02-471LF]	470 Ohm [CAY16-4700F4LF]	470 Ohm [CR1206-FX-4700ELF]
470 Ohm [4814P-2-471]	470 Ohm [4818P-T01-471]	470 Ohm [CAY16-471J2LF]	470 Ohm [CR1206-JW-471ELF]
470 Ohm [4814P-2-471LF]	470 Ohm [4820P-1-471]	470 Ohm [CAY16-471J4LF]	470 Ohm [CR1206-JW-471GLF]
470 Ohm [4814P-T01-471]	470 Ohm [4820P-2-471]	470 Ohm [CAY16-471J8LF]	470 Ohm [CR2512-JW-471ELF]
470 Ohm [4814P-T01-471LF]	470 Ohm [4820P-2-471LF]	470 Ohm [CAY17-471JALF]	470 Ohm [CRM1206-JW-471ELF]
470 Ohm [4814P-T02-471]	470 Ohm [4820P-T01-471]	470 Ohm [CR0201-JW-471GLF]	470 Ohm [CRM2010-JW-471ELF]
470 Ohm [4814P-T02-471LF]	470 Ohm [4820P-T01-471LF]	470 Ohm [CR0402-FX-4700GLF]	470 Ohm [CRM2512-FX-4700ELF]
470 Ohm [4816P-1-471]	470 Ohm [4820P-T02-471]	470 Ohm [CR0402-JW-471GLF]	470 Ohm [CRM2512-JW-471ELF]
470 Ohm [4816P-1-471F]	470 Ohm [CAT10-471J4LF]	470 Ohm [CR0603-FX-4700ELF]	470 Ohm [CRT0805-BY-4700ELF]
470 Ohm [4816P-1-471LF]	470 Ohm [CAT16-4700F4LF]	470 Ohm [CR0603-JW-471ELF]	470 Ohm [PWR163S-25-4700J]
470 Ohm [4816P-2-471]	470 Ohm [CAT16-471J4LF]	470 Ohm [CR0603-JW-471GLF]	470 Ohm [PWR220T-20-4700F]
470 Ohm [4816P-2-471LF]	470 Ohm [CAT16-471J8LF]	470 Ohm [CR0805-FX-4700ELF]	470 Ohm [PWR220T-20-4700J]
470 Ohm [4816P-T01-471]	470 Ohm [CAT25-471JALF]	470 Ohm [CR0805-FX-4700GLF]	
470 Ohm [4816P-T01-471LF]	470 Ohm [CAY10-471J2LF]	470 Ohm [CR0805-JW-471ELF]	
470 Ohm [4816P-T02-471]	470 Ohm [CAY10-471J4LF]	470 Ohm [CR0805-JW-471GLF]	

Multisim 14.1 Base Edition Components

470 Ohm [PWR220T-35-4700J]	470 Ohm [PWR6327W4700J]	470 pF [C0603C471K1HACT U]	470 pF [C0805C471K1GACT U]
470 Ohm [PWR2615W4700J]	470 Ohm [PWR6327W4700JE]	470 pF [C0603C471K1RACT U]	470 pF [C0805C471K1RACT U]
470 Ohm [PWR2615W4700JE]	470 pF [C0402C471K1HACT U]	470 pF [C0603C471K2RACT U]	470 pF [C0805C471K2GACT U]
470 Ohm [PWR263S-20-4700F]	470 pF [C0402C471K3GACT U]	470 pF [C0603C471K3GACT U]	470 pF [C0805C471K2RACT U]
470 Ohm [PWR263S-20-4700J]	470 pF [C0402C471K3HACT U]	470 pF [C0603C471K3HACT U]	470 pF [C0805C471K3RACT U]
470 Ohm [PWR263S-20-4700JE]	470 pF [C0402C471K3RACT U]	470 pF [C0603C471K3RACT U]	470 pF [C0805C471K4RACT U]
470 Ohm [PWR263S-35-4700F]	470 pF [C0402C471K4RACT U]	470 pF [C0603C471K4RACT U]	470 pF [C0805C471K5GACT U]
470 Ohm [PWR263S-35-4700J]	470 pF [C0402C471K5HACT U]	470 pF [C0603C471K5GACT U]	470 pF [C0805C471K5RACT U]
470 Ohm [PWR4318W4700JE]	470 pF [C0402C471K5RACT U]	470 pF [C0603C471K5HACT U]	470 pF [C0805C471KARACT U]
470 Ohm [PWR4525W4700J]	470 pF [C0402C471K8RACT U]	470 pF [C0603C471K5RACT U]	470 pF [C1206C471K1GACT U]
470 Ohm [PWR4525W4700JE]	470 pF [C0402C471K9RACT U]	470 pF [C0603C471K8RACT U]	470 pF [C1206C471K2GACT U]
470 Ohm [PWR5322W4700JE]			

Multisim 14.1 Base Edition Components

470 pF [C1206C471K5GACT U]	470 pF [CA064C471K4RACT U]	470 uF [16SVPE470M]	470 uF [6SEPC470MW]
470 pF [C1206C471KBGAC TU]	470 pF [CA064C471K5GAC TU]	470 uF [2R5TPE470M7]	470 uF [6SEPC470MX]
470 pF [C1206C471KCGAC TU]	470 pF [CA064C471K5RACT U]	470 uF [2R5TPE470M9]	470 uF [6TPB470M]
470 pF [C1210C471K5GACT U]	470 pF [CA064C471K8RAC]	470 uF [2R5TPE470MF]	470 uF [6TPE470M]
470 pF [C1210C471KBGAC TU]	470 pF [GPC7.3471K63K31 TR12]	470 uF [2R5TPE470MI]	470 uF [6TPE470MAZU]
470 pF [C1210C471KCGAC TU]	470 pF [GPC7.3472K630K3 5TR12]	470 uF [2R5TPF470M6L]	470 uF [6TPE470MI]
470 pF [C1812C471K5GACT U]	470 pF [SPC7.3471K100K31 TR12]	470 uF [2R5TPF470M7L]	470 uF [6TPF470MAH]
470 pF [C1812C471KBGAC TU]	470 pF [SPC7.3471K250K31 TR12]	470 uF [2R5TPF470M6L]	470 uF [A700X477M002AT E007]
470 pF [C1825C471KBGAC TU]	470 pF [SPC7.3471K400K31 TR12]	470 uF [2R5TPF470M7L]	470 uF [A700X477M002AT E010]
470 pF [C2220C471KBGAC TU]	470 pF [SPC7.3471K630K31 TR12]	470 uF [2TPE470MAJGB]	470 uF [A700X477M002AT E015]
470 pF [C2225C471KBGAC TU]	470 pF [W2F11A4718AT1A]	470 uF [4TPE470MCL]	470 uF [A700X477M002AT E015]
	470 uF [16SEPC470M]	470 uF [4TPE470MFL]	470 uF [EEFCX0D471R]
		470 uF [4TPE470MIL]	470 uF [EEFCX0E471R]
		470 uF [4TPE470ML]	470 uF [EEFGX0D471L]
		470 uF [4TPF470ML]	470 uF [EEFGX0D471R]
			470 uF [EEFGX0E471L]

Multisim 14.1 Base Edition Components

470 uF [EEFGX0E471R]	470 uF [EEFSX0D471XE]	470 uF [T494D477M006AT]	470 uF [T495X477M004AT E100]
470 uF [EEFHX0D471R]	470 uF [EEFSX0E471E4]	470 uF [T494E477M006AT]	470 uF [T495X477M006AT E030]
470 uF [EEFHX0D471R4]	470 uF [EEFSX0E471ER]	470 uF [T494E477M010AT]	470 uF [T495X477M006AT E045]
470 uF [EEFHX0D471R6]	470 uF [EEFSX0E471XE]	470 uF [T494X477M004AT]	470 uF [T495X477M006AT E050]
470 uF [EEFHX0D471R9]	470 uF [ETPF470M5H]	470 uF [T494X477M006AT]	470 uF [T495X477M006AT E050]
470 uF [EEFHX0E471R]	470 uF [T489X477M006AT E200]	470 uF [T494X477M010AT]	470 uF [T495X477M006AT E065]
470 uF [EEFHX0E471R4]	470 uF [T491D477M004AT]	470 uF [T495D477M006AT E045]	470 uF [T495X477M010AT E045]
470 uF [EEFHX0E471R6]	470 uF [T491D477M006AT]	470 uF [T495D477M006AT E100]	470 uF [T495X477M010AT E050]
470 uF [EEFLX0D471R]	470 uF [T491E477M006AT]	470 uF [T495D477M006AT E125]	470 uF [T495X477M010AT E060]
470 uF [EEFLX0D471R4]	470 uF [T491E477M010AT]	470 uF [T495E477M006AT E040]	470 uF [T495X477M010AT E100]
470 uF [EEFLX0E471R]	470 uF [T491X477M004AT]	470 uF [T495X477M004AT E030]	470 uF [T495X477M010AT E200]
470 uF [EEFLX0E471R4]	470 uF [T491X477M006AT]	470 uF [T495X477M004AT E045]	470 uF [T510X477M006AT E030]
470 uF [EEFSX0D471E4]	470 uF [T491X477M010AT]		
470 uF [EEFSX0D471ER]	470 uF [T494D477M004AT]		

Multisim 14.1 Base Edition Components

470 uF [T513X477M006AH 6110]	470 uF [T520D477M2R5AT E006]	470 uF [T520X477M006AT E018]	470 uF [T525D477M2R5AT E025]
470 uF [T520C477M2R5AT E025]	470 uF [T520D477M2R5AT E007]	470 uF [T520X477M006AT E035]	470 uF [T528Z477M2R5AT E005]
470 uF [T520C477M2R5AT E045]	470 uF [T520D477M2R5AT E009]	470 uF [T520X477M006AT E040]	470 uF [T528Z477M2R5AT E009]
470 uF [T520D477M004AT E010]	470 uF [T520V477M002AT E040]	470 uF [T520Y477M006AT E010]	470 uF [T528Z477M2R5AT E012]
470 uF [T520D477M004AT E012]	470 uF [T520V477M2R5AT E007]	470 uF [T520Y477M006AT E015]	470 uF [T530D477M004AT E006]
470 uF [T520D477M004AT E015]	470 uF [T520V477M2R5AT E009]	470 uF [T520Y477M006AT E018]	470 uF [T530D477M004AT E010]
470 uF [T520D477M004AT E018]	470 uF [T520V477M2R5AT E012]	470 uF [T520Y477M006AT E025]	470 uF [T530D477M2R5AT E006]
470 uF [T520D477M004AT E025]	470 uF [T520V477M2R5AT E015]	470 uF [T522Y477M006AT E040]	470 uF [T530X477M006AT E004]
470 uF [T520D477M004AT E040]	470 uF [T520V477M2R5AT E018]	470 uF [T525D477M003AT E025]	470 uF [T530X477M006AT E005]
470 uF [T520D477M006AT E025]	470 uF [T520W477M006AT E055]	470 uF [T525D477M004AT E025]	470 uF [T530X477M006AT E006]
470 uF [T520D477M006AT E030]	470 uF [T520X477M006AT E010]	470 uF [T525D477M004AT E040]	470 uF [T530X477M006AT E010]

Multisim 14.1 Base Edition Components

470 uF [T530Y477M004AT E005]	470 uF [TPME477K006R00 23]	470 uF [TPSE477K006R004 5]	470 uF [TPSV477K006R005 5]
470 uF [T530Y477M006AT E005]	470 uF [TPME477K006R00 30]	470 uF [TPSE477K006R005 0]	470 uF [TPSV477K006R010 0]
470 uF [T543D477M2R5AT E007]	470 uF [TPME477K010R00 23]	470 uF [TPSE477K006R006 0]	470 uF [TPSV477K010R004 0]
470 uF [TAJC477K002RNJ]	470 uF [TPME477K010R00 30]	470 uF [TPSE477K006R010 0]	470 uF [TPSV477K010R006 0]
470 uF [TAJC477K004RNJ]	470 uF [TPSD477K004R004 5]	470 uF [TPSE477K006R020 0]	470 uF [TPSV477K010R010 0]
470 uF [TAJD477K004RNJ]	470 uF [TPSD477K004R010 0]	470 uF [TPSE477K010R004 5]	470 uF [TRJE477K006RRJ]
470 uF [TAJE477K004RNJ]	470 uF [TPSD477K006R010 0]	470 uF [TPSE477K010R005 0]	470 uF [TRMD477K004R00 35]
470 uF [TAJE477K006RNJ]	470 uF [TPSD477K006R020 0]	470 uF [TPSE477K010R006 0]	470 uF [TRME477K006R00 30]
470 uF [TAJE477K010RNJ]	470 uF [TPSE477K004R003 5]	470 uF [TPSE477K010R010 0]	470 uH [SDE0805A- 471K]
470 uF [TAJV477K006RNJ]	470 uF [TPSE477K004R004 5]	470 uF [TPSE477K010R020 0]	470 uH [SDE1006A- 471K]
470 uF [TAJV477K010RNJ]	470 uF [TPSE477K004R004 5]	470 uF [TPSE477K010R020 0]	470 uH [SDR0302- 471KL]
470 uF [TAJY477K004RNJ]	470 uF [TPSE477K004R010 0]	470 uF [TPSV477K006R004 0]	470 uH [SDR0403- 471KL]
470 uF [TPME477K006R00 18]			470 uH [SDR0503- 471KL]

Multisim 14.1 Base Edition Components

470 uH [SDR0603-471KL]	470 uH [SDR7045-471K]	470 uH [SRR1208-471KL]	475 kOhm [CR0402-FX-4753GLF]
470 uH [SDR0604-471KL]	470 uH [SRN1060-471M]	470 uH [SRR1210-471M]	475 kOhm [CR0603-FX-4753ELF]
470 uH [SDR0703-471KL]	470 uH [SRR0603-471KL]	470 uH [SRR1210A-471M]	475 kOhm [CR0805-FX-4753ELF]
470 uH [SDR0805-471KL]	470 uH [SRR0604-471KL]	470 uH [SRR1240-471K]	475 kOhm [CR1206-FX-4753ELF]
470 uH [SDR0906-471KL]	470 uH [SRR0735A-471M]	470 uH [SRR1260-471K]	475 Ohm [CAT16-4750F4LF]
470 uH [SDR1005-471KL]	470 uH [SRR0745A-471M]	470 uH [SRR1260A-471K]	475 Ohm [CAY16-4750F4LF]
470 uH [SDR1006-471KL]	470 uH [SRR0804-471K]	470 uH [SRR1280-471K]	475 Ohm [CR0402-FX-4750GLF]
470 uH [SDR1030-471K]	470 uH [SRR0805-471K]	470 uH [SRR1806-471M]	475 Ohm [CR0603-FX-4750ELF]
470 uH [SDR1045-471K]	470 uH [SRR0905-471K]	470 uH [SRR4028-471Y]	475 Ohm [CR0805-FX-4750ELF]
470 uH [SDR1305-471K]	470 uH [SRR0906-471YL]	470 uH [SRR5028-471Y]	475 Ohm [CR1206-FX-4750ELF]
470 uH [SDR1307-471KL]	470 uH [SRR0908-471YL]	470 uH [SRR6028-471Y]	475 Ohm [CRM1206-FX-4750ELF]
470 uH [SDR1307A-471KL]	470 uH [SRR1003-471Y]	470 uH [SRR6603-471ML]	475 Ohm [CRT0603-BY-4750ELF]
470 uH [SDR1806-471KL]	470 uH [SRR1005-471K]	470 uH [SRR7032-471M]	48.7 kOhm [CR0201-FW-4872GLF]
470 uH [SDR6603-471M]	470 uH [SRR1205-471KL]	470 uH [SRR7045-471M]	
470 uH [SDR7030-471K]	470 uH [SRR1206-471KL]	47151-0001	
		47272-0001	

Multisim 14.1 Base Edition Components

48.7 kOhm [CR0402-FX- 4872GLF]	4814P-3-181/391	4816P-3-181/391LF	4816P-T03-121/471
	4814P-3-202/202	4816P-3-221/182	4816P-T03-122/562
48.7 kOhm [CR0603-FX- 4872ELF]	4814P-3-202/202LF	4816P-3-221/221	4816P-T03-151/151
	4814P-3-221/331	4816P-3-221/331	4816P-T03-161/241
48.7 kOhm [CR0805-FX- 4872ELF]	4814P-3-262/362	4816P-3-221/331LF	4816P-T03-181/301
	4814P-3-271/271	4816P-3-222/222	4816P-T03-181/391
48.7 kOhm [CR1206-FX- 4872ELF]	4814P-3-331/391	4816P-3-222/562	4816P-T03- 181/391L
	4814P-3-331/471	4816P-3-271/471	4816P-T03-221/221
	4814P-3-331/471LF	4816P-3-302/622	4816P-T03-221/271
48.7 kOhm [CRT1206-BY- 4872ELF]	4814P-3-501/501	4816P-3-302/622LF	4816P-T03- 221/271L
	4814P-3-800/211	4816P-3-331/331	4816P-T03-221/331
48.7 kOhm [CRT1206-FZ- 4872ELF]	4814P-3-800/211LF	4816P-3-331/391	4816P-T03-221/331
	4814P-T03-111/221	4816P-3-331/391LF	4816P-T03- 221/331L
48.7 Ohm [CR0402- FX-48R7GLF]	4814P-T03-221/331	4816P-3-331/470	4816P-T03-222/562
	4814P-T03-262/362	4816P-3-331/471	4816P-T03-271/471
48.7 Ohm [CR0603- FX-48R7ELF]	4814P-T03-331/391	4816P-3-331/471LF	4816P-T03-302/622
	4814P-T03-331/471	4816P-3-391/391	4816P-T03- 302/622L
48.7 Ohm [CR0805- FX-48R7ELF]	4814P-T03-501/501	4816P-3-471/681	4816P-T03-331/391
48.7 Ohm [CR1206- FX-48R7ELF]	4816P-3-101/101	4816P-3-681/102	4816P-T03-331/391
	4816P-3-101/101LF	4816P-3-800/211	4816P-T03-331/391
48.7 Ohm [CRT1206-FZ- 48R7ELF]	4816P-3-102/332	4816P-T03- 102/102F	4816P-T03- 331/391L
4814P-3-102/102LF	4816P-3-121/471	4816P-T03-102/202	4816P-T03-331/471
4814P-3-111/221	4816P-3-161/241	4816P-T03-102/332	4816P-T03- 331/471L
4814P-3-161/241	4816P-3-181/271	4816P-T03-121/121	
	4816P-3-181/391		

Multisim 14.1 Base Edition Components

4816P-T03-332/472	487 kOhm [CR0402-FX- 4873GLF]	49.9 kOhm [CR0402-FX- 4992GLF]	49.9 Ohm [CAY16- 49R9F4LF]
4816P-T03-681/102			49.9 Ohm [CR0201- FW-49R9GLF]
4816P-T03-820/131	487 kOhm [CR0603-FX- 4873ELF]	49.9 kOhm [CR0603-FX- 4992ELF]	49.9 Ohm [CR0402- FX-49R9GLF]
4818P-T03-221/182	487 kOhm [CR0805-FX- 4873ELF]	49.9 kOhm [CR0805-FX- 4992ELF]	49.9 Ohm [CR0603- FX-49R9ELF]
4818P-T03-221/331			
4818P-T03-331/471			
4820P-3-104/273	487 kOhm [CR1206-FX- 4873ELF]	49.9 kOhm [CR1206-FX- 4992ELF]	49.9 Ohm [CR0603- FX-49R9GLF]
4820P-3-152/332			49.9 Ohm [CR0805- FX-49R9ELF]
4820P-3-221/331	487 kOhm [CRT1206-FZ- 4873ELF]	49.9 kOhm [CRM2512-FX- 4992ELF]	49.9 Ohm [CR0805- FX-49R9GLF]
4820P-3-225/225			
4820P-3-271/471			
4820P-3-331/331LF	487 Ohm [CR0402- FX-4870GLF]	49.9 kOhm [CRT0402-BY- 4992GLF]	49.9 Ohm [CR1206- FX-49R9ELF]
4820P-3-331/471			
4820P-3-331/471LF	487 Ohm [CR0603- FX-4870ELF]	49.9 kOhm [CRT0603-BY- 4992ELF]	49.9 Ohm [CR2512- FX-49R9ELF]
4820P-3-331/680	487 Ohm [CR0805- FX-4870ELF]		49.9 Ohm [CRM1206-FX- 49R9ELF]
4820P-3-331/681		49.9 kOhm [CRT0805-BY- 4992ELF]	
4820P-3-332/332LF	487 Ohm [CR1206- FX-4870ELF]		49.9 Ohm [CRM2010-FX- 49R9ELF]
4820P-3-471/681	487 Ohm [CRT1206-FZ- 4870ELF]	49.9 kOhm [CRT0805-DZ- 4992ELF]	
4820P-T03-104/273			49.9 Ohm [CRM2512-FX- 49R9ELF]
4820P-T03-152/332	49 mOhm [PWR4412- 2SCR0490F]	49.9 Ohm [CAT16- 49R9F4GLF]	
4820P-T03-181/391			49.9 Ohm
4820P-T03-221/331	49.9 kOhm [CAT16- 4992F4LF]	49.9 Ohm [CAT16- 49R9F4LF]	[CRT0402-FZ- 49R9GLF]
4820P-T03-271/471			
4820P-T03-331/471	49.9 kOhm [CAY16- 4992F4LF]	49.9 Ohm [CAT16- 49R9F8LF]	
4820P-T03-331/681			

Multisim 14.1 Base Edition Components

49.9 Ohm [CRT0805-FV-49R9ELF]	499 kOhm [CRM2512-FX-4993ELF]	499 Ohm [CRT0402-BV-4990GLF]	5 kOhm [4116R-2-502LF]
49.9 Ohm [CRT1206-BY-49R9ELF]	499 kOhm [CRT0603-BY-4993ELF]	499 Ohm [CRT0402-BY-4990GLF]	5 kOhm [4306R-101-502]
49.9 Ohm [CRT1206-DY-49R9ELF]	499 kOhm [CRT0805-DZ-4993ELF]	499 Ohm [CRT1206-DY-4990ELF]	5 kOhm [4308H-102-502]
499 kOhm [CAY16-4993F4LF]	499 kOhm [CRT1206-BY-4993ELF]	499 Ohm [PWR5322W4990FE]	5 kOhm [4310R-101-502]
499 kOhm [CHV1206-FX-4993ELF]	499 Ohm [CAT16-4990F4LF]	4Line_Bussed	5 kOhm [4310R-101-502LF]
499 kOhm [CHV2512-FX-4993ELF]	499 Ohm [CAY16-4990F4LF]	4Line_Isolated	5 kOhm [4605X-101-502LF]
499 kOhm [CR0402-FX-4993GLF]	499 Ohm [CR0402-FX-4990GLF]	4Line_Terminator	5 kOhm [4605X-AP1-502LF]
499 kOhm [CR0603-FX-4993ELF]	499 Ohm [CR0603-FX-4990ELF]	4POS_ROTARY	5 kOhm [4608X-102-502LF]
499 kOhm [CR0805-FX-4993ELF]	499 Ohm [CR0805-FX-4990ELF]	4V_0.5W	5 kOhm [4608X-AP1-502LF]
499 kOhm [CR1206-FX-4993ELF]	499 Ohm [CR1206-FX-4990ELF]	5 kOhm [4108R-1-502LF]	5 kOhm [4610H-101-502LF]
499 kOhm [CR1206-FX-4993ELF]	499 Ohm [CR2512-FX-4990ELF]	5 kOhm [4114R-1-502LF]	5 kOhm [4610X-101-502LF]
499 kOhm [CRM1206-FX-4993ELF]	499 Ohm [CRM1206-FX-4990ELF]	5 kOhm [4114R-2-502]	5 kOhm [4816P-1-502]
499 kOhm [CRM1206-FX-4993ELF]	499 Ohm [CRM2512-FX-4990ELF]	5 kOhm [4116R-1-502]	5 kOhm [4816P-2-502]
		5 kOhm [4116R-1-502LF]	5 kOhm [4816P-2-502LF]
		5 kOhm [4116R-2-502]	

Multisim 14.1 Base Edition Components

5 kOhm [PWR221T-30-5001F]	5 mOhm [PWR6327WR005J]	5 Ohm [PWR263S-35-5R00J]	5 uH [SRR6040A-5R0Y]
5 kOhm [PWR263S-35-5001F]	5 mOhm [PWR6327WR005JE]	5 Ohm [PWR263S-35-5R00JE]	5 uH [SRU1038-5R0Y]
5 mH [SDR0503-502JL]	5 Ohm [PWR163S-25-5R00F]	5 Ohm [PWR3014W5R00JE]	5 uH [SRU1038A-5R0Y]
5 mOhm [CRE2512-FZ-R005E-2]	5 Ohm [PWR163S-25-5R00FE]	5 Ohm [PWR4318W5R00JE]	5.1 kOhm [4114R-1-512]
5 mOhm [CRE2512-FZ-R005E-3]	5 Ohm [PWR163S-25-5R00J]	5 Ohm [PWR4525W5R00J]	5.1 kOhm [4114R-1-512LF]
5 mOhm [CRF0805-FX-R005ELF]	5 Ohm [PWR163S-25-5R00JE]	5 Ohm [PWR5322W5R00JE]	5.1 kOhm [4114R-2-512]
5 mOhm [CRF2512-FX-R005ELF]	5 Ohm [PWR2010W5R00JE]	5 Ohm [PWR6327W5R00J]	5.1 kOhm [4116R-1-512]
5 mOhm [CRF2512-JX-R005ELF]	5 Ohm [PWR220T-20-5R00J]	5 uH [SDR0603-5R0ML]	5.1 kOhm [4116R-1-512LF]
5 mOhm [PWR4412-2SBR0050F]	5 Ohm [PWR220T-35-5R00F]	5 uH [SRR0804-5R0M]	5.1 kOhm [4116R-2-512]
5 mOhm [PWR4412-2SBR0050J]	5 Ohm [PWR220T-35-5R00J]	5 uH [SRR1205-5R0ML]	5.1 kOhm [4116R-2-512LF]
5 mOhm [PWR4412-2SCR0050F]	5 Ohm [PWR221T-30-5R00F]	5 uH [SRR1206-5R0ML]	5.1 kOhm [4306M-101-512]
5 mOhm [PWR4412-2SDR0050F]	5 Ohm [PWR221T-30-5R00J]	5 uH [SRR5018-5R0Y]	5.1 kOhm [4306M-101-512LF]
5 mOhm [PWR4412-2SDR0050J]	5 Ohm [PWR263S-20-5R00F]	5 uH [SRR6028-5R0Y]	5.1 kOhm [4306M-102-512]
	5 Ohm [PWR263S-35-5R00F]	5 uH [SRR6038-5R0Y]	5.1 kOhm [4306R-101-512LF]

Multisim 14.1 Base Edition Components

5.1 kOhm [4308M-101-512]	5.1 kOhm [4310R-101-512LF]	5.1 kOhm [4814P-2-512]	5.1 kOhm [CAT16-512J8LF]
5.1 kOhm [4308M-101-512LF]	5.1 kOhm [4416P-1-512]	5.1 kOhm [4814P-2-512LF]	5.1 kOhm [CAT25-512JALF]
5.1 kOhm [4308M-102-512]	5.1 kOhm [4605X-101-512LF]	5.1 kOhm [4816P-1-512]	5.1 kOhm [CAY10-512J4LF]
5.1 kOhm [4308M-102-512LF]	5.1 kOhm [4605X-AP1-512LF]	5.1 kOhm [4816P-1-512F]	5.1 kOhm [CAY16-512J4LF]
5.1 kOhm [4308R-101-512]	5.1 kOhm [4606X-101-512LF]	5.1 kOhm [4816P-1-512LF]	5.1 kOhm [CAY17-512JALF]
5.1 kOhm [4308R-101-512LF]	5.1 kOhm [4606X-102-512LF]	5.1 kOhm [4816P-2-512]	5.1 kOhm [CR0402-FX-5101GLF]
5.1 kOhm [4308R-102-512]	5.1 kOhm [4607X-101-512LF]	5.1 kOhm [4816P-2-512LF]	5.1 kOhm [CR0402-JW-512GLF]
5.1 kOhm [4308R-102-512LF]	5.1 kOhm [4608X-101-512LF]	5.1 kOhm [4816P-T01-512]	5.1 kOhm [CR0603-FX-5101ELF]
5.1 kOhm [4310H-101-512]	5.1 kOhm [4608X-102-512LF]	5.1 kOhm [4816P-T01-512LF]	5.1 kOhm [CR0603-JW-512ELF]
5.1 kOhm [4310H-101-512LF]	5.1 kOhm [4608X-AP1-512LF]	5.1 kOhm [4816P-T02-512]	5.1 kOhm [CR0805-FX-5101ELF]
5.1 kOhm [4310M-101-512]	5.1 kOhm [4609X-101-512LF]	5.1 kOhm [4816P-T02-512LF]	5.1 kOhm [CR0805-FX-5101GLF]
5.1 kOhm [4310M-101-512LF]	5.1 kOhm [4610X-101-512LF]	5.1 kOhm [4820P-1-512F]	5.1 kOhm [CR0805-JW-512ELF]
5.1 kOhm [4310M-102-512]	5.1 kOhm [4610X-102-512LF]	5.1 kOhm [4820P-2-512]	5.1 kOhm [CR1206-FX-5101ELF]
5.1 kOhm [4310M-102-512LF]	5.1 kOhm [4814P-1-512]	5.1 kOhm [CAT10-512J4LF]	5.1 kOhm [CR1206-JW-512ELF]
5.1 kOhm [4310R-101-512]	5.1 kOhm [4814P-1-512LF]	5.1 kOhm [CAT16-512J4LF]	5.1 kOhm [CR2010-JW-512ELF]

Multisim 14.1 Base Edition Components

5.1 kOhm [CR2512-JW-512ELF]	5.1 MOhm [CR0603-JW-515ELF]	5.1 nF [C2225C512KBGAC TU]	5.1 Ohm [CRL0603-FW-5R10ELF]
5.1 kOhm [CRM1206-JW-512ELF]	5.1 MOhm [CR0805-JW-515ELF]	5.1 Ohm [CAT10-5R1J4LF]	5.1 Ohm [CRL0603-JW-5R10ELF]
5.1 kOhm [CRM2512-FX-5101ELF]	5.1 MOhm [CR1206-JW-515ELF]	5.1 Ohm [CAT16-5R1J2LF]	5.1 Ohm [CRL0805-FW-5R10ELF]
5.1 kOhm [CRT0603-BY-5101ELF]	5.1 nF [C0603C512K3HACT U]	5.1 Ohm [CAT16-5R1J4GLF]	5.1 Ohm [CRL1206-FW-5R10ELF]
5.1 kOhm [CRT0603-FX-5101ELF]	5.1 nF [C0603C512K5HACT U]	5.1 Ohm [CAT16-5R1J4LF]	5.1 Ohm [CRL2010-FW-5R10ELF]
5.1 kOhm [CRT0603-FY-5101ELF]	5.1 nF [C0805C512K1GACT U]	5.1 Ohm [CAY10-5R1J2LF]	5.1 Ohm [CRL2010-JW-5R10ELF]
5.1 kOhm [CRT0805-BW-5101ELF]	5.1 nF [C0805C512K1HACT U]	5.1 Ohm [CAY10-5R1J4LF]	5.1 Ohm [CRL2512-FW-5R10ELF]
5.1 kOhm [CRT0805-FX-5101ELF]	5.1 nF [C0805C512K3HACT U]	5.1 Ohm [CR0402-J/-5R1GLF]	5.1 Ohm [CRM1206-JW-5R1ELF]
5.1 kOhm [CRT1206-BY-5101ELF]	5.1 nF [C0805C512K5HACT U]	5.1 Ohm [CR0603-J/-5R1ELF]	5.1 Ohm [CRM2512-FX-5R10ELF]
5.1 MOhm [4604X-102-515LF]	5.1 nF [C0805C512K3HACT U]	5.1 Ohm [CR0603-JW-5R1GLF]	5.1 Ohm [CRM2512-JW-5R1ELF]
5.1 MOhm [CHV0603-FX-5104ELF]	5.1 nF [C1206C512K5GACT U]	5.1 Ohm [CR0603-JW-5R1GLF]	5.1 Ohm [CRT0805-BW-5R10ELF]
5.1 MOhm [CR0402-JW-515GLF]	5.1 nF [C2220C512KBGAC TU]	5.1 Ohm [CR1206-J/-5R1ELF]	5.1 Ohm [CRT0805-BW-5R10ELF]
		5.1 Ohm [CR1206-J/-5R1GLF]	5.1 Ohm [FW10A5R10JA]
		5.1 Ohm [CR2010-J/-5R1ELF]	5.1 Ohm [FW30A5R10JA]
			5.1 Ohm [FW50A5R10JA]

Multisim 14.1 Base Edition Components

5.1 Ohm [PWR4318W5R10JE]	5.11 kOhm [CRT0805-CX- 5111ELF]	5.36 kOhm [CR0805-FX- 5361ELF]	5.6 kOhm [4114R- 1-562LF]
5.1 Ohm [PWR5322W5R10JE]	5.11 MOhm [CR1206-FW- 5114ELF]	5.36 kOhm [CR1206-FX- 5361ELF]	5.6 kOhm [4114R- 2-562]
5.11 kOhm [CAY16- 5111F4LF]	5.11 Ohm [CRM1206-FX- 5R11ELF]	5.36 kOhm [CRT0603-BY- 5361ELF]	5.6 kOhm [4116R- 1-562]
5.11 kOhm [CR0402-FX- 5111GLF]	5.2 uH [SRU1038- 5R2Y]	5.4 uH [SRR5018- 5R4Y]	5.6 kOhm [4116R- 1-562LF]
5.11 kOhm [CR0603-FX- 5111ELF]	5.23 kOhm [CR0402-FX- 5231GLF]	5.49 kOhm [CAY16- 5491F4LF]	5.6 kOhm [4116R- 2-562]
5.11 kOhm [CR0805-FX- 5111ELF]	5.23 kOhm [CR0603-FX- 5231ELF]	5.49 kOhm [CR0402-FX- 5491GLF]	5.6 kOhm [4116R- 2-562LF]
5.11 kOhm [CR1206-FX- 5111ELF]	5.23 kOhm [CR0805-FX- 5231ELF]	5.49 kOhm [CR0603-FX- 5491ELF]	5.6 kOhm [4304M- 102-562]
5.11 kOhm [CRT0402-BY- 5111GLF]	5.23 kOhm [CR1206-FX- 5231ELF]	5.49 kOhm [CR0805-FX- 5491ELF]	5.6 kOhm [4306H- 102-562]
5.11 kOhm [CRT0402-FZ- 5111GLF]	5.23 kOhm [CRT0603-BY- 5231ELF]	5.49 kOhm [CR1206-FX- 5491ELF]	5.6 kOhm [4306H- 102-562LF]
5.11 kOhm [CRT0603-BY- 5111ELF]	5.3 uH [SRR5028- 5R3Y]	5.49 kOhm [CRT0603-CW- 5491ELF]	5.6 kOhm [4306M- 101-562LF]
5.11 kOhm [CRT0805-BW- 5111ELF]	5.36 kOhm [CR0402-FX- 5361GLF]	5.49 kOhm [CRT0805-CX- 5491ELF]	5.6 kOhm [4306R- 101-562]
	5.36 kOhm [CR0603-FX- 5361ELF]	5.6 kOhm [4114R- 1-562]	5.6 kOhm [4306R- 101-562LF]

Multisim 14.1 Base Edition Components

5.6 kOhm [4306R-102-562]	5.6 kOhm [4310M-101-562]	5.6 kOhm [4606H-101-562LF]	5.6 kOhm [4612X-102-562LF]
5.6 kOhm [4306R-102-562LF]	5.6 kOhm [4310R-101-562]	5.6 kOhm [4606X-101-562LF]	5.6 kOhm [4814P-1-562]
5.6 kOhm [4308H-101-562]	5.6 kOhm [4310R-101-562LF]	5.6 kOhm [4606X-102-562LF]	5.6 kOhm [4814P-2-562]
5.6 kOhm [4308H-101-562LF]	5.6 kOhm [4310R-102-562]	5.6 kOhm [4606X-AP1-562LF]	5.6 kOhm [4814P-T01-562]
5.6 kOhm [4308H-102-562LF]	5.6 kOhm [4310R-102-562LF]	5.6 kOhm [4606X-AP2-562LF]	5.6 kOhm [4814P-T01-562LF]
5.6 kOhm [4308M-101-562]	5.6 kOhm [4416P-2-562]	5.6 kOhm [4607X-101-562LF]	5.6 kOhm [4814P-T02-562]
5.6 kOhm [4308M-101-562LF]	5.6 kOhm [4416P-T01-562]	5.6 kOhm [4608X-101-562LF]	5.6 kOhm [4814P-T02-562LF]
5.6 kOhm [4308M-102-562]	5.6 kOhm [4416P-T02-562]	5.6 kOhm [4608X-102-562LF]	5.6 kOhm [4816P-1-562]
5.6 kOhm [4308M-102-562LF]	5.6 kOhm [4420P-2-562]	5.6 kOhm [4608X-AP2-562LF]	5.6 kOhm [4816P-1-562LF]
5.6 kOhm [4308R-101-562]	5.6 kOhm [4420P-2-562LF]	5.6 kOhm [4609H-101-562LF]	5.6 kOhm [4816P-2-562]
5.6 kOhm [4308R-101-562LF]	5.6 kOhm [4420P-T02-562]	5.6 kOhm [4609M-101-562LF]	5.6 kOhm [4816P-2-562LF]
5.6 kOhm [4308R-102-562]	5.6 kOhm [4604X-101-562LF]	5.6 kOhm [4609X-101-562LF]	5.6 kOhm [4816P-T01-562]
5.6 kOhm [4308R-102-562LF]	5.6 kOhm [4604X-102-562LF]	5.6 kOhm [4610X-101-562LF]	5.6 kOhm [4816P-T01-562LF]
5.6 kOhm [4309R-101-562]	5.6 kOhm [4605H-101-562FLF]	5.6 kOhm [4610X-102-562LF]	5.6 kOhm [4816P-T02-562]
5.6 kOhm [4309R-101-562LF]	5.6 kOhm [4605X-101-562LF]	5.6 kOhm [4610X-AP1-562LF]	5.6 kOhm [4816P-T02-562LF]

Multisim 14.1 Base Edition Components

5.6 kOhm [4820P-T02-562]	5.6 kOhm [CR0603-JW-562ELF]	5.6 mH [SRR0906-562YL]	5.6 nF [C0402C562K5RACTU]
5.6 kOhm [CAT10-562J4LF]	5.6 kOhm [CR0603-JW-562GLF]	5.6 mH [SRR1208-562KL]	5.6 nF [C0603C562K1RACTU]
5.6 kOhm [CAT16-5601F4LF]	5.6 kOhm [CR0805-FX-5601ELF]	5.6 MOhm [4608X-102-565LF]	5.6 nF [C0603C562K3GACTU]
5.6 kOhm [CAT16-5601F8LF]	5.6 kOhm [CR0805-JW-562ELF]	5.6 MOhm [4610X-102-565LF]	5.6 nF [C0603C562K3HACTU]
5.6 kOhm [CAT16-562J4LF]	5.6 kOhm [CR1206-FX-5601ELF]	5.6 MOhm [CAT25-565JALF]	5.6 nF [C0603C562K3RACTU]
5.6 kOhm [CAT16-562J8LF]	5.6 kOhm [CR1206-JW-562ELF]	5.6 MOhm [CR0402-JW-565GLF]	5.6 nF [C0603C562K4RACTU]
5.6 kOhm [CAT25-562JALF]	5.6 kOhm [CR2010-JW-562ELF]	5.6 MOhm [CR0603-JW-565ELF]	5.6 nF [C0603C562K5HACTU]
5.6 kOhm [CAY10-562J4LF]	5.6 kOhm [CR2512-JW-562ELF]	5.6 MOhm [CR0805-JW-565ELF]	5.6 nF [C0603C562K5RACTU]
5.6 kOhm [CAY16-5601F4LF]	5.6 kOhm [CRM2512-JW-562ELF]	5.6 MOhm [CR1206-JW-565ELF]	5.6 nF [C0603C562K8RACTU]
5.6 kOhm [CAY16-562J4LF]	5.6 kOhm [CRT0805-PV-5601ELF]	5.6 MOhm [CR2512-JW-565ELF]	5.6 nF [C0402C562K3RACTU]
5.6 kOhm [CAY16-562J8LF]	5.6 kOhm [PWR263S-35-5601FE]	5.6 nF [C0402C562K4RACTU]	5.6 nF [C0805C562K1GACTU]
5.6 kOhm [CAY17-562JALF]	5.6 kOhm [PWR4525W5601J]	5.6 nF [C0402C562K4RACTU]	5.6 nF [C0805C562K1HACTU]
5.6 kOhm [CR0402-FX-5601GLF]	5.6 mH [SDR0503-562JL]		
5.6 kOhm [CR0402-JW-562GLF]	5.6 mH [SDR0906-562KL]		
5.6 kOhm [CR0603-FX-5601ELF]			

Multisim 14.1 Base Edition Components

5.6 nF [C0805C562K1RACT U]	5.6 nF [C1206C562K5GACT U]	5.6 nF [GMC5.7562K50J31 TR12]	5.6 nF [MMC7.3562K50K3 1TR12]
5.6 nF [C0805C562K2RACT U]	5.6 nF [C1206C562K5RACT U]	5.6 nF [GMC7.3562K100K3 1TR12]	5.6 nF [MMC7.3562K63K3 1TR12]
5.6 nF [C0805C562K3GACT U]	5.6 nF [C1206C562KARACT U]	5.6 nF [GMC7.3562K400K3 1TR12]	5.6 Ohm [CR0402- J/-5R6GLF]
5.6 nF [C0805C562K3HACT U]	5.6 nF [C1210C562K5GACT U]	5.6 nF [GMC7.3562K63K31 TR12]	5.6 Ohm [CR0603- J/-5R6ELF]
5.6 nF [C0805C562K3RACT U]	5.6 nF [C1210C562K5RACT U]	5.6 nF [GMC7.3563K100K3 3TR12]	5.6 Ohm [CR0805- J/-5R6ELF]
5.6 nF [C0805C562K4RACT U]	5.6 nF [C1210C562KARACT U]	5.6 nF [MMC5.7562K100J 31TR12]	5.6 Ohm [CR2010- J/-5R6ELF]
5.6 nF [C0805C562K5HACT U]	5.6 nF [C1812C562K2GACT U]	5.6 nF [MMC5.7562K250J 31TR12]	5.6 Ohm [CRL0603- FW-5R60ELF]
5.6 nF [C0805C562K5RACT U]	5.6 nF [C2220C562KBGAC TU]	5.6 nF [MMC5.7562K50J3 1TR12]	5.6 Ohm [CRL0805- FW-5R60ELF]
5.6 nF [C0805C562KARACT U]	5.6 nF [C2225C562KBGAC TU]	5.6 nF [MMC7.3562K100K 31TR12]	5.6 Ohm [CRL1206- FW-5R60ELF]
5.6 nF [C1206C562K1RACT U]	5.6 nF [GMC5.7562K100J3 1TR12]	5.6 nF [MMC7.3562K250K 31TR12]	5.6 Ohm [CRL1206- JW-5R60ELF]
5.6 nF [C1206C562K2RACT U]	5.6 nF [GMC5.7562K250J3 1TR12]	5.6 nF [MMC7.3562K400K 33TR12]	5.6 Ohm [CRL2010- FW-5R60ELF]
			5.6 Ohm [CRL2512- FW-5R60ELF]

Multisim 14.1 Base Edition Components

5.6 Ohm [CRM1206-FX- 5R60ELF]	5.6 Ohm [PWR263S-20- 5R60J]	5.6 uF [MDC10565K100A5 5P5TUBE]	5.6 uH [SDR0703- 5R6ML]
5.6 Ohm [CRM2512-JW- 5R6ELF]	5.6 Ohm [PWR263S-35- 5R60F]	5.6 uF [MDC10565K50A54 P3TUBE]	5.6 uH [SDR0805- 5R6ML]
5.6 Ohm [CRT0805- BW-5R60ELF]	5.6 Ohm [PWR263S-35- 5R60FE]	5.6 uF [MDC10565K50A54 P4TUBE]	5.6 uH [SDR1006- 5R6ML]
5.6 Ohm [CRT0805- FZ-5R60ELF]	5.6 Ohm [PWR263S-35- 5R60J]	5.6 uF [MDC15565K100B5 5P3TUBE]	5.6 uH [SDR1307- 5R6ML]
5.6 Ohm [FW10A5R60JA]	5.6 uF [25TQC5R6M]	5.6 uF [MDC15565K100B5 5P4TUBE]	5.6 uH [SDR1307A- 5R6M]
5.6 Ohm [FW20A5R60JA]	5.6 uF [C0805C565K9PACT U]	5.6 uF [MDC15565K50B53 P3TUBE]	5.6 uH [SDR1806- 5R6ML]
5.6 Ohm [FW30A5R60JA]	5.6 uF [C1206C565K4RACT U]	5.6 uF [MDS15565K50B53 P3TUBE]	5.6 uH [SRN5020- 5R6M]
5.6 Ohm [PWR163S-25- 5R60F]	5.6 uF [C1206C565K8RACT U]	5.6 uH [SDE0604A- 5R6M]	5.6 uH [SRP1040- 5R6M]
5.6 Ohm [PWR163S-25- 5R60J]	5.6 uF [C1206C565K9RACT U]	5.6 uH [SDE0805A- 5R6M]	5.6 uH [SRP1235- 5R6M]
5.6 Ohm [PWR220T-20- 5R60F]	5.6 uF [C1210C565K4PACT U]	5.6 uH [SDE1006A- 5R6M]	5.6 uH [SRP1245A- 5R6M]
5.6 Ohm [PWR220T-20- 5R60J]	5.6 uF [MDC10565K100A5 5P4TUBE]	5.6 uH [SDR0302- 5R6ML]	5.6 uH [SRP1265A- 5R6M]
5.6 Ohm [PWR263S-20- 5R60F]		5.6 uH [SDR0403- 5R6ML]	5.6 uH [SRP1270- 5R6M]
		5.6 uH [SDR0604- 5R6ML]	5.6 uH [SRP1770TA-5R6M]
			5.6 uH [SRP4012TA-5R6M]

Multisim 14.1 Base Edition Components

5.6 uH [SRP4020-5R6M]	5.6 uH [SRR1260-5R6Y]	5.62 kOhm [CRT0402-FZ-5621GLF]	5.76 kOhm [CRT0603-BY-5761ELF]
5.6 uH [SRP4020TA-5R6M]	5.6 uH [SRR1260A-5R6Y]	5.62 kOhm [CRT0603-BY-5621ELF]	5.8 uH [SRP1205-5R6Y]
5.6 uH [SRP5015TA-5R6M]	5.6 uH [SRR1280-5R6Y]	5.62 kOhm [CRT0805-BY-5621ELF]	5.9 kOhm [CR0402-FX-5901GLF]
5.6 uH [SRP5030T-5R6M]	5.6 uH [SRR4018-5R6Y]	5.62 kOhm [CRT1206-FZ-5621ELF]	5.9 kOhm [CR0603-FX-5901ELF]
5.6 uH [SRP5030TA-5R6M]	5.6 uH [SRR4028-5R6Y]	5.62 Ohm [CRM1206-FX-5R62ELF]	5.9 kOhm [CR0805-FX-5901ELF]
5.6 uH [SRP6540-5R6M]	5.6 uH [SRR7045-5R6M]	5.62 Ohm [CRT0805-BY-5R62ELF]	5.9 kOhm [CR1206-FX-5901ELF]
5.6 uH [SRP7028A-5R6M]	5.62 kOhm [CAY16-5621F4LF]	5.62 Ohm [CRT0805-BY-5R62ELF]	5_AMP
5.6 uH [SRP7030-5R6FM]	5.62 kOhm [CR0402-FX-5621GLF]	5.76 kOhm [CR0402-FX-5761GLF]	50 kOhm [4108R-1-503]
5.6 uH [SRP7050TA-5R6M]	5.62 kOhm [CR0603-FX-5621ELF]	5.76 kOhm [CR0603-FX-5761ELF]	50 kOhm [4108R-1-503LF]
5.6 uH [SRR0805-5R6M]	5.62 kOhm [CR0805-FX-5621ELF]	5.76 kOhm [CR0805-FX-5761ELF]	50 kOhm [4116R-1-503]
5.6 uH [SRR0906-5R6ML]	5.62 kOhm [CR1206-FX-5621ELF]	5.76 kOhm [CR1206-FX-5761ELF]	50 kOhm [4116R-2-503]
5.6 uH [SRR0908-5R6ML]	5.62 kOhm [CR2010-FX-5621ELF]	5.76 kOhm [CRT0603-BX-5761ELF]	50 kOhm [4116R-2-503LF]
5.6 uH [SRR1210-5R6Y]	5.62 kOhm [CRT0402-BY-5621GLF]		50 kOhm [4604X-102-503LF]
5.6 uH [SRR1210A-5R6Y]			50 kOhm [4820P-2-503]
5.6 uH [SRR1240-5R6M]			

Multisim 14.1 Base Edition Components

50 kOhm [PWR221T-30-5002J]	50 mOhm [CRM1206-FX-R050ELF]	50 mOhm [PWR2615WR050FE]	50 mOhm [PWR6327WR050JE]
50 kOhm [PWR263S-35-5002F]	50 mOhm [CRM2010-FX-R050ELF]	50 mOhm [PWR2615WR050J]	50 Ohm [4116R-1-500]
50 mOhm [CRA2512-FZ-R050ELF]	50 mOhm [CRM2512-FX-R050ELF]	50 mOhm [PWR2615WR050JE]	50 Ohm [4116R-1-500LF]
50 mOhm [CRA2512-JZ-R050ELF]	50 mOhm [PWR163S-25-R050J]	50 mOhm [PWR4412-2SBR0500F]	50 Ohm [4304M-102-500]
50 mOhm [CRF2512-FZ-R050ELF]	50 mOhm [PWR163S-25-R050JE]	50 mOhm [PWR4412-2SCR0500F]	50 Ohm [4306R-101-500]
50 mOhm [CRL0805-FW-R050ELF]	50 mOhm [PWR1913WR050F]	50 mOhm [PWR4412-2SCR0500J]	50 Ohm [4306R-101-500LF]
50 mOhm [CRL0805-JW-R050ELF]	50 mOhm [PWR1913WR050FE]	50 mOhm [PWR4412-2SDR0500F]	50 Ohm [4308R-101-500]
50 mOhm [CRL2010-FW-R050ELF]	50 mOhm [PWR1913WR050J]	50 mOhm [PWR4412-2SDR0500J]	50 Ohm [4308R-101-500LF]
50 mOhm [CRL2512-FW-R050ELF]	50 mOhm [PWR1913WR050JE]	50 mOhm [PWR4525WR050J]	50 Ohm [4308R-102-500]
50 mOhm [CRL2512-JW-R050ELF]	50 mOhm [PWR220T-20-R050J]	50 mOhm [PWR4525WR050JE]	50 Ohm [4310R-101-500]
50 mOhm [CRM0805-FW-R050ELF]	50 mOhm [PWR221T-30-R050J]	50 mOhm [PWR4525W-R050JE]	50 Ohm [4310R-101-500LF]
	50 mOhm [PWR2615WR050F]	50 mOhm [PWR6327WR050J]	50 Ohm [4310R-102-500]
			50 Ohm [4420P-2-500]

Multisim 14.1 Base Edition Components

50 Ohm [4420P-T02-500]	50 Ohm [PWR221T-30-50R0F]	500 mOhm [PWR163S-25-R500J]	500 mOhm [PWR263S-20-R500J]
50 Ohm [4606X-102-500LF]	50 Ohm [PWR221T-30-50R0J]	500 mOhm [PWR2010WR500FE]	500 mOhm [PWR263S-35-R500F]
50 Ohm [4816P-T02-500]	50 Ohm [PWR263S-20-50R0F]	500 mOhm [PWR2010WR500JE]	500 mOhm [PWR263S-35-R500J]
50 Ohm [CAT25-500JALF]	50 Ohm [PWR263S-20-50R0J]	500 mOhm [PWR220T-20-R500F]	500 mOhm [PWR3014WR500JE]
50 Ohm [PWR163S-25-50R0F]	50 Ohm [PWR263S-20-50R0JE]	500 mOhm [PWR220T-20-R500J]	500 mOhm [PWR4318WR500JE]
50 Ohm [PWR163S-25-50R0FE]	50 Ohm [PWR263S-35-50R0F]	500 mOhm [PWR221T-30-R500F]	500 mOhm [PWR4525WR500J]
50 Ohm [PWR163S-25-50R0J]	50 Ohm [PWR263S-35-50R0FE]	500 mOhm [PWR221T-30-R500J]	500 mOhm [PWR5322WR500JE]
50 Ohm [PWR163S-25-50R0JE]	50 uH [SRR1205-500YL]	500 mOhm [PWR221T-50-R500F]	500 mOhm [PWR6327WR500F]
50 Ohm [PWR1913W50R0J]	50_AMP	500 mOhm [PWR2615WR500F]	500 nH [SRN8040-R50Y]
50 Ohm [PWR220T-20-50R0F]	500 mOhm [CRM2512-FX-R500ELF]	500 mOhm [PWR2615WR500FE]	500 nH [SRP1040-R50M]
50 Ohm [PWR220T-20-50R0J]	500 mOhm [PWR163S-25-R500F]	500 mOhm [PWR2615WR500F]	500 nH [SRP1250-R50M]
50 Ohm [PWR220T-35-50R0J]	500 mOhm [PWR163S-25-R500FE]	500 mOhm [PWR263S-20-R500F]	500 Ohm [4116R-1-501]
			500 Ohm [4116R-1-501LF]

Multisim 14.1 Base Edition Components

500 Ohm [4306R-101-501]	51 kOhm [4116R-1-513LF]	51 kOhm [4814P-2-513]	51 kOhm [CR0201-FW-5102GLF]
500 Ohm [4306R-101-501LF]	51 kOhm [4306R-101-513]	51 kOhm [4814P-2-513LF]	51 kOhm [CR0402-FX-5102GLF]
500 Ohm [4605X-101-501LF]	51 kOhm [4308R-102-513]	51 kOhm [4814P-T02-513]	51 kOhm [CR0402-JW-513GLF]
500 Ohm [4816P-1-501LF]	51 kOhm [4308R-102-513LF]	51 kOhm [4816P-1-513]	51 kOhm [CR0603-FX-5102ELF]
500 Ohm [4816P-T01-501]	51 kOhm [4310H-101-513]	51 kOhm [4816P-1-513LF]	51 kOhm [CR0603-JW-513ELF]
500 Ohm [4816P-T01-501LF]	51 kOhm [4310M-101-513]	51 kOhm [4816P-2-513]	51 kOhm [CR0805-FX-5102ELF]
500 Ohm [CAT16-501J4LF]	51 kOhm [4310R-101-513]	51 kOhm [4816P-2-513LF]	51 kOhm [CR0805-JW-513ELF]
500 Ohm [PWR221T-30-5000F]	51 kOhm [4310R-101-513LF]	51 kOhm [4820P-2-513]	51 kOhm [CR1206-FX-5102ELF]
500 Ohm [PWR263S-35-5000J]	51 kOhm [4310R-102-513]	51 kOhm [4820P-T02-513]	51 kOhm [CR1206-JW-513ELF]
500 uOhm [CST0612-FC-R0005-E]	51 kOhm [4604X-101-513LF]	51 kOhm [CAT16-513J4LF]	51 kOhm [CR2010-JW-513ELF]
50A02CH-TL-E	51 kOhm [4606X-101-513LF]	51 kOhm [CAT25-513JALF]	51 kOhm [CR2512-JW-513ELF]
50A02CH-TL-H	51 kOhm [4608X-101-513LF]	51 kOhm [CAY10-513J4LF]	51 kOhm [CRM2010-FX-5102ELF]
50C02CH-TL-E	51 kOhm [4609X-101-513LF]	51 kOhm [CAY16-5102F4LF]	51 kOhm [CRM2512-FX-5102ELF]
50C02MH-TL-E	51 kOhm [4610X-101-513LF]	51 kOhm [CAY16-513J4LF]	51 kOhm [CRT0805-BW-5102ELF]
50C02SS-TL-E	51 kOhm [4610X-102-513LF]	51 kOhm [CAY17-513JALF]	

Multisim 14.1 Base Edition Components

51 kOhm [CRT1206-BW- 5102ELF]	51 Ohm [4306R- 101-510]	51 Ohm [4605X- 101-510LF]	51 Ohm [4816P- T02-510]
51 mF [C0805C519K3GACT U]	51 Ohm [4306R- 101-510LF]	51 Ohm [4606X- 101-510LF]	51 Ohm [4816P- T02-510LF]
51 mF [C0805C519KBGAC TU]	51 Ohm [4308H- 102-510]	51 Ohm [4606X- 102-510LF]	51 Ohm [4820P-1- 510]
51 MOhm [CHV2010-JW- 516ELF]	51 Ohm [4308R- 101-510]	51 Ohm [4608X- 101-510LF]	51 Ohm [4820P-1- 510LF]
51 mOhm [PWR4412- 2SCR0510F]	51 Ohm [4308R- 102-510]	51 Ohm [4608X- 102-510LF]	51 Ohm [4820P- T01-510]
51 Ohm [4114R-1- 510]	51 Ohm [4308R- 102-510LF]	51 Ohm [4609X- 101-510LF]	51 Ohm [CAT10- 510J4LF]
51 Ohm [4114R-1- 510LF]	51 Ohm [4310M- 101-510]	51 Ohm [4610X- 101-510LF]	51 Ohm [CAT16- 510J2LF]
51 Ohm [4116R-1- 510]	51 Ohm [4310M- 101-510LF]	51 Ohm [4610X- 102-510LF]	51 Ohm [CAT16- 510J4GLF]
51 Ohm [4116R-1- 510LF]	51 Ohm [4310R- 101-510]	51 Ohm [4814P- T01-510]	51 Ohm [CAT16- 510J4LF]
51 Ohm [4116R-1- 510]	51 Ohm [4310R- 101-510LF]	51 Ohm [4816P-1- 510]	51 Ohm [CAT16- 510J8LF]
51 Ohm [4116R-1- 510LF]	51 Ohm [4310R- 102-510]	51 Ohm [4816P-1- 510LF]	51 Ohm [CAT16- 51R0F4LF]
51 Ohm [4116R-2- 510]	51 Ohm [4310R- 102-510LF]	51 Ohm [4816P-2- 510]	51 Ohm [CAT16- 51R0F8LF]
51 Ohm [4116R-2- 510LF]	51 Ohm [4311R- 101-510]	51 Ohm [4816P-2- 510LF]	51 Ohm [CAT25- 510JALF]
51 Ohm [4304M- 102-510]	51 Ohm [4416P-1- 510]	51 Ohm [4816P- T01-510]	51 Ohm [CAY10- 510J2LF]
51 Ohm [4304M- 102-510LF]	51 Ohm [4416P- T01-510]	51 Ohm [4816P- T01-510LF]	51 Ohm [CAY10- 510J4LF]

Multisim 14.1 Base Edition Components

51 Ohm [CAY16-510J2LF]	51 Ohm [CR1206-JW-510ELF]	51 pF [C0603C510K2GACT U]	51 pF [C1825C510KBGAC TU]
51 Ohm [CAY16-510J4LF]	51 Ohm [CR1206-JW-510GLF]	51 pF [C0603C510K5GACT U]	51 pF [C2220C510KBGAC TU]
51 Ohm [CAY16-510J8LF]	51 Ohm [CR2010-JW-510ELF]	51 pF [C0805C510K1GACT U]	51 pF [C2225C510KBGAC TU]
51 Ohm [CAY16-51R0F4LF]	51 Ohm [CR2512-JW-510ELF]	51 pF [C0805C510K2GACT U]	51.1 kOhm [CAY16-5112F4LF]
51 Ohm [CAY17-510JALF]	51 Ohm [CRM0805-FX-51R0ELF]	51 pF [C0805C510K5GACT U]	51.1 kOhm [CR0402-FX-5112GLF]
51 Ohm [CR0201-JW-510GLF]	51 Ohm [CRM1206-FX-51R0ELF]	51 pF [C0805C510KBGAC TU]	51.1 kOhm [CR0603-FX-5112ELF]
51 Ohm [CR0402-FX-51R0GLF]	51 Ohm [CRM2010-FX-51R0ELF]	51 pF [C0805C510KCGAC TU]	51.1 kOhm [CR0603-FX-5112HLF]
51 Ohm [CR0402-JW-510GLF]	51 Ohm [CRM2512-FX-51R0ELF]	51 pF [C1206C510K5GACT U]	51.1 kOhm [CR0805-FX-5112ELF]
51 Ohm [CR0603-FX-51R0ELF]	51 Ohm [CRM2512-JW-510ELF]	51 pF [C1206C510KBGAC TU]	51.1 kOhm [CR1206-FX-5112ELF]
51 Ohm [CR0603-JW-510ELF]	51 Ohm [PWR220T-20-51R0F]	51 pF [C1210C510KBGAC TU]	51.1 kOhm [CRT0603-BX-5112ELF]
51 Ohm [CR0805-FX-51R0ELF]	51 Ohm [PWR2615W51R0F]	51 pF [C0402C510K5GACT U]	51.1 kOhm [CRT0603-BY-5112ELF]
51 Ohm [CR0805-FX-51R0GLF]	51 pF [C0402C510K5GACT U]	51 pF [C1812C510KBGAC TU]	
51 Ohm [CR0805-JW-510ELF]			
51 Ohm [CR1206-FX-51R0ELF]			

Multisim 14.1 Base Edition Components

51.1 kOhm [CRT0603-FZ- 5112ELF]	51.1 Ohm [CRT0402-FZ- 51R1GLF]	510 kOhm [CR1206-FX- 5103ELF]	510 mOhm [CRL2512-FW- R510ELF]
51.1 kOhm [CRT0603-PW- 5112ELF]	510 kOhm [4606X- 101-514LF]	510 kOhm [CR1206-JW- 514ELF]	510 mOhm [CRM0805-FX- R510ELF]
51.1 kOhm [CRT0805-BY- 5112ELF]	510 kOhm [4608X- 101-514LF]	510 kOhm [CR2010-JW- 514ELF]	510 mOhm [CRM1206-FX- R510ELF]
51.1 kOhm [CRT0805-FY- 5112ELF]	510 kOhm [CAT10- 514J4LF]	510 mOhm [CRL0603-FW- R510ELF]	510 mOhm [CRM2010-FX- R510ELF]
51.1 Ohm [CAT16- 51R1F4LF]	510 kOhm [CAY10- 514J4LF]	510 mOhm [CRL0603-JW- R510ELF]	510 mOhm [CRM2512-FX- R510ELF]
51.1 Ohm [CR0402- FX-51R1GLF]	510 kOhm [CAY16- 514J4LF]	510 mOhm [CRL0805-FW- R510ELF]	510 mOhm [CRM2512-JX- R510ELF]
51.1 Ohm [CR0603- FX-51R1ELF]	510 kOhm [CR0402-FX- 5103GLF]	510 mOhm [CRL0805-JW- R510ELF]	510 mOhm [PWR4318WR510JE]
51.1 Ohm [CR0603- FX-51R1GLF]	510 kOhm [CR0402-JW- 514GLF]	510 mOhm [CRL1206-FW- R510ELF]	510 mOhm [PWR5322WR510JE]
51.1 Ohm [CR0805- FX-51R1ELF]	510 kOhm [CR0603-FX- 5103ELF]	510 mOhm [CRL1206-JW- R510ELF]	510 Ohm [4114R-1- 511]
51.1 Ohm [CR1206- FX-51R1ELF]	510 kOhm [CR0603-JW- 514ELF]	510 mOhm [CRL2010-FW- R510ELF]	510 Ohm [4114R-1- 511LF]
51.1 Ohm [CR2010- FX-51R1ELF]	510 kOhm [CR0805-FX- 5103ELF]	510 mOhm [CRL2010-JW- R510ELF]	510 Ohm [4116R-1- 511]
51.1 Ohm [CR2512- FX-51R1ELF]	510 kOhm [CR0805-JW- 514ELF]		
51.1 Ohm [CRM0805-FX- 51R1ELF]			

Multisim 14.1 Base Edition Components

510 Ohm [4116R-1-511LF]	510 Ohm [4310R-101-511LF]	510 Ohm [4814P-1-511]	510 Ohm [CAY10-511J2LF]
510 Ohm [4116R-2-511]	510 Ohm [4310R-102-511]	510 Ohm [4814P-2-511]	510 Ohm [CAY10-511J4LF]
510 Ohm [4306R-101-511]	510 Ohm [4604X-102-511LF]	510 Ohm [4814P-2-511LF]	510 Ohm [CAY16-511J4LF]
510 Ohm [4306R-101-511LF]	510 Ohm [4605X-101-511LF]	510 Ohm [4814P-T02-511]	510 Ohm [CAY17-511JALF]
510 Ohm [4308H-101-511]	510 Ohm [4606X-101-511LF]	510 Ohm [4814P-T02-511LF]	510 Ohm [CR0201-FW-5100GLF]
510 Ohm [4308H-102-511]	510 Ohm [4606X-102-511LF]	510 Ohm [4816P-1-511]	510 Ohm [CR0402-FX-5100GLF]
510 Ohm [4308H-102-511LF]	510 Ohm [4607X-101-511LF]	510 Ohm [4816P-1-511LF]	510 Ohm [CR0402-JW-511GLF]
510 Ohm [4308R-101-511]	510 Ohm [4608X-101-511LF]	510 Ohm [4816P-2-511]	510 Ohm [CR0603-FX-5100ELF]
510 Ohm [4308R-101-511LF]	510 Ohm [4608X-102-511LF]	510 Ohm [4816P-2-511LF]	510 Ohm [CR0603-JW-511ELF]
510 Ohm [4308R-102-511]	510 Ohm [4608X-AP2-511LF]	510 Ohm [4816P-T01-511]	510 Ohm [CR0805-FX-5100ELF]
510 Ohm [4308R-102-511LF]	510 Ohm [4609X-101-511LF]	510 Ohm [4816P-T01-511LF]	510 Ohm [CR0805-FX-5100GLF]
510 Ohm [4309R-101-511]	510 Ohm [4610X-101-511LF]	510 Ohm [4816P-T02-511]	510 Ohm [CR0805-JW-511ELF]
510 Ohm [4310M-101-511]	510 Ohm [4610X-102-511LF]	510 Ohm [CAT10-511J4LF]	510 Ohm [CR1206-FX-5100ELF]
510 Ohm [4310M-101-511LF]	510 Ohm [4610X-AP1-511LF]	510 Ohm [CAT16-511J4LF]	510 Ohm [CR1206-JW-511ELF]
510 Ohm [4310R-101-511]	510 Ohm [4612H-101-511LF]	510 Ohm [CAT25-511JALF]	510 Ohm [CR2010-FX-5100ELF]

Multisim 14.1 Base Edition Components

510 Ohm [CR2010-JW-511ELF]	510 pF [C0603C511K5HACT U]	5103309-7	511 Ohm [CR2010-FX-5110ELF]
510 Ohm [CR2512-JW-511ELF]	510 pF [C0603C511K8GACT U]	5103309-8	511 Ohm [CR2512-FX-5110ELF]
510 Ohm [CRM2512-FX-5100ELF]	510 pF [C0805C511K5GACT U]	5103310-1	511 Ohm [CRT0402-FZ-5110GLF]
510 Ohm [CRM2512-JW-511ELF]	510 pF [C1206C511K1GACT U]	5103310-5	511 Ohm [CRT0603-BY-5110ELF]
510 Ohm [CRT0603-FY-5100ELF]	510 pF [C1206C511KBGAC TU]	5103310-6	511 Ohm [CRT0805-CX-5110ELF]
510 Ohm [PWR220T-20-5100F]	510 pF [C1210C511KBGAC TU]	5103310-7	5-1814400-1
510 pF [C0402C511K1HACT U]	510 pF [C1812C511KBGAC TU]	5103310-8	52.3 kOhm [CR0402-FX-5232GLF]
510 pF [C0402C511K3HACT U]	510 pF [C1825C511KBGAC TU]	511 kOhm [CR0402-FX-5113GLF]	52.3 kOhm [CR0603-FX-5232ELF]
510 pF [C0402C511K5HACT U]	510 pF [C2220C511KBGAC TU]	511 kOhm [CR0603-FX-5113ELF]	52.3 kOhm [CR0805-FX-5232ELF]
510 pF [C0603C511K1HACT U]	510 pF [C2225C511KBGAC TU]	511 kOhm [CR0805-FX-5113ELF]	52.3 kOhm [CRT0805-BW-5232ELF]
510 pF [C0603C511K3HACT U]	5103309-1	511 Ohm [CAY16-5110F4LF]	52.3 Ohm [CR0603-FX-52R3ELF]
510 pF [C0603C511K5GACT U]	5103309-5	511 Ohm [CR0402-FX-5110GLF]	52.3 Ohm [CR0805-FX-52R3ELF]
	5103309-6	511 Ohm [CR0603-FX-5110ELF]	
		511 Ohm [CR0805-FX-5110ELF]	
		511 Ohm [CR1206-FX-5110ELF]	

Multisim 14.1 Base Edition Components

52.3 Ohm [CR1206-FX-52R3ELF]	53.6 kOhm [CR0603-FX-5362GLF]	536 kOhm [CR0805-FX-5363ELF]	54.9 Ohm [CR0402-FX-54R9GLF]
5227222-3			54.9 Ohm [CR0603-FX-54R9ELF]
5227677-1	53.6 kOhm [CR0805-FX-5362ELF]	536 kOhm [CR1206-FX-5363ELF]	54.9 Ohm [CR0805-FX-54R9ELF]
523 kOhm [CR0402-FX-5233GLF]	53.6 kOhm [CR1206-FX-5362ELF]	536 Ohm [CR0402-FX-5360GLF]	54.9 Ohm [CR1206-FX-54R9ELF]
523 kOhm [CR0603-FX-5233ELF]	53.6 kOhm [CRT0805-BY-5362ELF]	536 Ohm [CR0603-FX-5360ELF]	540 nH [SRP1205-R30Y]
523 kOhm [CR0805-FX-5233ELF]	53.6 Ohm [CR0603-FX-53R6ELF]	536 Ohm [CR0805-FX-5360ELF]	5414337-1
523 kOhm [CR1206-FX-5233ELF]	53.6 Ohm [CR0805-FX-53R6ELF]	536 Ohm [CR1206-FX-5360ELF]	549 kOhm [CR0201-FW-5493GLF]
523 Ohm [CR0402-FX-5230GLF]	53.6 Ohm [CR1206-FX-53R6ELF]	54.9 kOhm [CAY16-5492F4LF]	549 kOhm [CR0402-FX-5493GLF]
523 Ohm [CR0603-FX-5230ELF]	53.6 Ohm [CR2010-FX-53R6ELF]	54.9 kOhm [CR0402-FX-5492GLF]	549 kOhm [CR0603-FX-5493ELF]
523 Ohm [CR0805-FX-5230ELF]	532903-2	54.9 kOhm [CR0603-FX-5492ELF]	549 kOhm [CR0805-FX-5493ELF]
523 Ohm [CR1206-FX-5230ELF]	532903-6	54.9 kOhm [CR0805-FX-5492ELF]	549 kOhm [CR1206-FX-5493ELF]
53.6 kOhm [CR0402-FX-5362GLF]	534206-5	54.9 kOhm [CR1206-FX-5492ELF]	549 Ohm [CR0402-FX-5490GLF]
53.6 kOhm [CR0603-FX-5362ELF]	534237-3		549 Ohm [CR0603-FX-5490ELF]
	534237-6		549 Ohm [CR0805-FX-5490ELF]
	534237-8		
	536 kOhm [CR0603-FX-5363ELF]	54.9 Ohm [CAY16-54R9F4LF]	
		54.9 Ohm [CR0201-FW-54R9GLF]	

Multisim 14.1 Base Edition Components

549 Ohm [CR1206-FX-5490ELF]	56 kOhm [4116R-2-563LF]	56 kOhm [4604X-102-563LF]	56 kOhm [4816P-1-563LF]
549 Ohm [CRT1206-BV-5490ELF]	56 kOhm [4306R-101-563]	56 kOhm [4605X-101-563LF]	56 kOhm [4816P-2-563]
549 Ohm [CRT1206-BW-5490ELF]	56 kOhm [4306R-101-563LF]	56 kOhm [4606X-101-563LF]	56 kOhm [4816P-2-563LF]
549 Ohm [CRT1206-BY-5490ELF]	56 kOhm [4306R-102-563]	56 kOhm [4606X-102-563LF]	56 kOhm [4816P-T01-563]
549 Ohm [CRT1206-BY-5490ELF]	56 kOhm [4306R-102-563LF]	56 kOhm [4608M-102-563LF]	56 kOhm [4816P-T01-563LF]
55 mOhm [CRA2512-JZ-R055ELF]	56 kOhm [4308R-101-563]	56 kOhm [4608X-101-563LF]	56 kOhm [4816P-T02-563]
55 Ohm [4416P-2-550]	56 kOhm [4308R-101-563LF]	56 kOhm [4608X-102-563LF]	56 kOhm [4816P-T02-563LF]
555_VIRTUAL	56 kOhm [4308R-102-563]	56 kOhm [4608X-AP2-563LF]	56 kOhm [4820P-2-563]
5558067-1	56 kOhm [4308R-102-563LF]	56 kOhm [4609X-101-563LF]	56 kOhm [CAT10-563J4LF]
56 kOhm [4114R-1-563]	56 kOhm [4310R-101-563]	56 kOhm [4610X-101-563LF]	56 kOhm [CAT16-5602F4LF]
56 kOhm [4114R-1-563LF]	56 kOhm [4310R-101-563LF]	56 kOhm [4610X-102-563LF]	56 kOhm [CAT16-563J4LF]
56 kOhm [4114R-2-563]	56 kOhm [4310R-102-563]	56 kOhm [4612X-102-563LF]	56 kOhm [CAT16-563J8LF]
56 kOhm [4114R-2-563LF]	56 kOhm [4310R-102-563LF]	56 kOhm [4814P-2-563]	56 kOhm [CAT25-563JALF]
56 kOhm [4116R-1-563]	56 kOhm [4420P-2-563]	56 kOhm [4814P-T02-563]	56 kOhm [CAY16-5602F4LF]
56 kOhm [4116R-1-563LF]	56 kOhm [4420P-T02-563]	56 kOhm [4816P-1-563]	56 kOhm [CAY16-563J4LF]
56 kOhm [4116R-2-563]			

Multisim 14.1 Base Edition Components

56 kOhm [CAY16-563J8LF]	56 kOhm [CRT0603-AX-5602ELF]	56 nF [C0805C563K2RACTU]	56 nF [C1206C563K5HACTU]
56 kOhm [CAY17-563JALF]	56 kOhm [PWR163S-25-5602F]	56 nF [C0805C563K3RACTU]	56 nF [C1206C563K5RACTU]
56 kOhm [CR0201-FW-5602GLF]	56 kOhm [PWR220T-20-5602F]	56 nF [C0805C563K4RACTU]	56 nF [C1206C563KARACTU]
56 kOhm [CR0402-FX-5602GLF]	56 mF [C0805C569KBGAC TU]	56 nF [C0805C563K5RACTU]	56 nF [C1206C563M5UAC TU]
56 kOhm [CR0603-FX-5602ELF]	56 nF [C0402C563K4RACTU]	56 nF [C0805C563K8RACTU]	56 nF [C1206F563K1RACTU]
56 kOhm [CR0603-JW-563GLF]	56 nF [C0402C563K8RACTU]	56 nF [C0805F563K3RACTU]	56 nF [C1206F563K3RACTU]
56 kOhm [CR0805-FX-5602ELF]	56 nF [C0402C563K9RACTU]	56 nF [C0805F563K4RACTU]	56 nF [C1206F563K4RACTU]
56 kOhm [CR0805-FX-5602GLF]	56 nF [C0603C563K3RACTU]	56 nF [C0805F563K5RACTU]	56 nF [C1206F563K5RACTU]
56 kOhm [CR1206-FX-5602ELF]	56 nF [C0603C563K4RACTU]	56 nF [C1206C563K1RACTU]	56 nF [C1210C563K1GACTU]
56 kOhm [CR1206-JW-563ELF]	56 nF [C0603C563K5RACTU]	56 nF [C1206C563K3HACTU]	56 nF [C1210C563K1HACTU]
56 kOhm [CR1206-JW-563GLF]	56 nF [C0805C563K1RACTU]	56 nF [C1206C563K3RACTU]	56 nF [C1210C563K1RACTU]

Multisim 14.1 Base Edition Components

56 nF [C1210C563K2RACT U]	56 nF [C2220C563K1GACT U]	56 nF [MDC15563K100B5 3P3TUBE]	56 Ohm [4116R-1- 560]
56 nF [C1210C563K3HACT U]	56 nF [C2220C563K2GACT U]	56 nF [MDC15563K250B5 3P3TUBE]	56 Ohm [4116R-1- 560LF]
56 nF [C1210C563K5GACT U]	56 nF [C2220C563K5GACT U]	56 nF [MDC15563K400B5 3P3TUBE]	56 Ohm [4116R-2- 560]
56 nF [C1210C563K5HACT U]	56 nF [GMC5.7563K50J31 TR12]	56 nF [MDC15563K50B53 P3TUBE]	56 Ohm [4304M- 102-560]
56 nF [C1210C563K5RACT U]	56 nF [GMC7.3562K250K3 1TR12]	56 nF [MDC15563K630B5 3P3TUBE]	56 Ohm [4306R- 101-560]
56 nF [C1210C563KARACT U]	56 nF [GMC7.3563K63K31 TR12]	56 nF [MDK15563K250B5 3P3TUBE]	56 Ohm [4306R- 102-560]
56 nF [C1812C563K1GACT U]	56 nF [MDC10563K100A5 2P3TUBE]	56 nF [MDK15563K400B5 3P3TUBE]	56 Ohm [4306R- 102-560LF]
56 nF [C1812C563K1HACT U]	56 nF [MDC10563K250A5 2P3TUBE]	56 nF [MDK15563K50B53 P3TUBE]	56 Ohm [4308M- 102-560]
56 nF [C1812C563K1RACT U]	56 nF [MDC10563K400A5 2P3TUBE]	56 nF [MDS15563K400B5 3P3TUBE]	56 Ohm [4308M- 102-560LF]
56 nF [C1812C563K5GACT U]	56 nF [MDC10563K50A52 P3TUBE]	56 nF [MDS15563K50B53 P3TUBE]	56 Ohm [4308R- 101-560]
56 nF [C1812C563K5HACT U]	56 nF [MDC10563K630A5 2P3TUBE]	56 Ohm [4114R-1- 560]	56 Ohm [4308R- 101-560LF]
		56 Ohm [4114R-1- 560LF]	

Multisim 14.1 Base Edition Components

56 Ohm [4309R-101-560]	56 Ohm [4420P-T02-560]	56 Ohm [4612X-102-560LF]	56 Ohm [CAT16-560J8LF]
56 Ohm [4310H-101-560]	56 Ohm [4604X-101-560LF]	56 Ohm [4614X-102-560LF]	56 Ohm [CAT16-56R0F4LF]
56 Ohm [4310H-101-560LF]	56 Ohm [4604X-102-560LF]	56 Ohm [4814P-T01-560]	56 Ohm [CAT25-560JALF]
56 Ohm [4310M-102-560]	56 Ohm [4605M-101-560LF]	56 Ohm [4816P-1-560]	56 Ohm [CAY10-560J4LF]
56 Ohm [4310M-102-560LF]	56 Ohm [4605X-101-560LF]	56 Ohm [4816P-1-560LF]	56 Ohm [CAY16-560J4LF]
56 Ohm [4310R-101-560]	56 Ohm [4606M-101-560LF]	56 Ohm [4816P-2-560]	56 Ohm [CAY16-560J8LF]
56 Ohm [4310R-101-560LF]	56 Ohm [4606X-101-560LF]	56 Ohm [4816P-2-560LF]	56 Ohm [CAY16-56R0F4LF]
56 Ohm [4310R-102-560]	56 Ohm [4606X-102-560LF]	56 Ohm [4816P-T01-560]	56 Ohm [CAY17-560JALF]
56 Ohm [4310R-102-560LF]	56 Ohm [4607X-101-560LF]	56 Ohm [4816P-T01-560LF]	56 Ohm [CR0402-FX-56R0GLF]
56 Ohm [4416P-1-560]	56 Ohm [4608X-101-560LF]	56 Ohm [4816P-T02-560]	56 Ohm [CR0402-JW-560GLF]
56 Ohm [4416P-2-560]	56 Ohm [4608X-102-560LF]	56 Ohm [4816P-T02-560LF]	56 Ohm [CR0603-FX-56R0ELF]
56 Ohm [4416P-T01-560]	56 Ohm [4608X-AP2-560LF]	56 Ohm [4818P-T01-560]	56 Ohm [CR0603-JW-560ELF]
56 Ohm [4420P-1-560]	56 Ohm [4609X-101-560LF]	56 Ohm [4820P-T01-560]	56 Ohm [CR0805-FX-56R0ELF]
56 Ohm [4420P-2-560]	56 Ohm [4610X-101-560LF]	56 Ohm [CAT10-560J4LF]	56 Ohm [CR0805-FX-56R0GLF]
56 Ohm [4420P-T01-560]	56 Ohm [4610X-102-560LF]	56 Ohm [CAT16-560J4LF]	56 Ohm [CR0805-JW-560ELF]

Multisim 14.1 Base Edition Components

56 Ohm [CR0805-JW-560GLF]	56 Ohm [PWR221T-30-56R0J]	56 pF [C0603C560K1GACTU]	56 pF [C1206C560K5GACTU]
56 Ohm [CR1206-FX-56R0ELF]	56 Ohm [PWR263S-20-56R0F]	56 pF [C0603C560K2GACTU]	56 pF [C1206C560KBGACTU]
56 Ohm [CR1206-FX-56R0GLF]	56 Ohm [PWR263S-20-56R0FE]	56 pF [C0603C560K3GACTU]	56 pF [C1206C560KDGACTU]
56 Ohm [CR2512-FX-56R0ELF]	56 Ohm [PWR263S-20-56R0J]	56 pF [C0603C560K5GACTU]	56 pF [C1210C560KBGACTU]
56 Ohm [CR2512-JW-560ELF]	56 Ohm [PWR263S-35-56R0F]	56 pF [C0805C560K1GACTU]	56 pF [C1812C560KBGACTU]
56 Ohm [CRM2512-FX-56R0ELF]	56 Ohm [PWR263S-35-56R0J]	56 pF [C0805C560K2GACTU]	56 pF [C1812C560KHGACTU]
56 Ohm [CRT0603-BY-56R0ELF]	56 pF [C0201C560K3GACTU]	56 pF [C0805C560K5GACTU]	56 pF [C1825C560KBGACTU]
56 Ohm [PWR163S-25-56R0F]	56 pF [C0201C560K8GACTU]	56 pF [C0805C560KBGACTU]	56 pF [C2220C560KBGACTU]
56 Ohm [PWR163S-25-56R0J]	56 pF [C0402C560K3GACTU]	56 pF [C0805C560KDGACTU]	56 pF [C2225C560KBGACTU]
56 Ohm [PWR220T-20-56R0F]	56 pF [C0402C560K5GACTU]	56 pF [C1206C560K1GACTU]	56 pF [CA064C560K5GACTU]
56 Ohm [PWR221T-30-56R0F]	56 pF [C0402C560K8GACTU]	56 pF [C1206C560K2GACTU]	56 uF [A700D566M008ATE015]

Multisim 14.1 Base Edition Components

56 uF [A700D566M008AT E018]	56 uF [T520T566M2R5AT E070]	56 uH [SDR1307- 560KL]	56 uH [SRR1208- 560YL]
56 uF [A700D566M010AT E015]	56 uH [SDE0403A- 560K]	56 uH [SDR1307A- 560K]	56 uH [SRR1210- 560M]
56 uF [A700D566M010AT E018]	56 uH [SDE0604A- 560K]	56 uH [SRP1770TA- 560M]	56 uH [SRR1210A- 560M]
56 uF [A700V566M006AT E018]	56 uH [SDE0805A- 560K]	56 uH [SRP7050TA- 560M]	56 uH [SRR1240- 560M]
56 uF [A700V566M006AT E018]	56 uH [SDE1006A- 560K]	56 uH [SRR0735A- 560M]	56 uH [SRR1260- 560M]
56 uF [A700V566M006AT E025]	56 uH [SDR0302- 560KL]	56 uH [SRR0745A- 560M]	56 uH [SRR1260A- 560M]
56 uF [A700V566M006AT E028]	56 uH [SDR0403- 560KL]	56 uH [SRR0804- 560K]	56 uH [SRR1280- 560M]
56 uF [EEFCX1D560R]	56 uH [SDR0503- 560KL]	56 uH [SRR0805- 560K]	56 uH [SRR4018- 560Y]
56 uF [EEFHX1D560R]	56 uH [SDR0603- 560KL]	56 uH [SRR0905- 560Y]	56 uH [SRR4028- 560Y]
56 uF [EEHZA1E560P]	56 uH [SDR0604- 560KL]	56 uH [SRR0906- 560ML]	56 uH [SRR5018- 560Y]
56 uF [EEHZA1J560P]	56 uH [SDR0703- 560KL]	56 uH [SRR0908- 560ML]	56 uH [SRR5028- 560Y]
56 uF [EEHZA1J560P]	56 uH [SDR0805- 560KL]	56 uH [SRR1003- 560M]	56 uH [SRR6028- 560Y]
56 uF [EEHZC1E560P]	56 uH [SDR0906- 560KL]	56 uH [SRR1005- 560Y]	56 uH [SRR6038- 560Y]
56 uF [EEHZC1J560P]	56 uH [SDR1006- 560KL]	56 uH [SRR1205- 560YL]	56 uH [SRR6040A- 560M]
56 uF [T520T566M2R5AT E040]	56 uH [SDR1105- 560KL]	56 uH [SRR1206- 560YL]	56 uH [SRR7045- 560M]

Multisim 14.1 Base Edition Components

56 uH [SRU1028-560Y]	56.2 Ohm [CAY16-56R2F4LF]	560 kOhm [4116R-1-564LF]	560 kOhm [4310R-102-564]
56 uH [SRU1028A-560Y]	56.2 Ohm [CR0201-FW-56R2GLF]	560 kOhm [4116R-2-564]	560 kOhm [4606X-101-564LF]
56 uH [SRU1048-560Y]	56.2 Ohm [CR0402-FX-56R2GLF]	560 kOhm [4116R-2-564LF]	560 kOhm [4606X-102-564LF]
56 uH [SRU1048A-560Y]	56.2 Ohm [CR0603-FX-56R2ELF]	560 kOhm [4306R-101-564]	560 kOhm [4608X-101-564LF]
56.2 kOhm [CAY16-5622F4LF]	56.2 Ohm [CR0805-FX-56R2ELF]	560 kOhm [4306R-102-564]	560 kOhm [4608X-102-564LF]
56.2 kOhm [CR0402-FX-5622GLF]	56.2 Ohm [CR1206-FX-56R2ELF]	560 kOhm [4306R-102-564LF]	560 kOhm [4609X-101-564LF]
56.2 kOhm [CR0603-FX-5622ELF]	56.2 Ohm [CR2512-FX-56R2ELF]	560 kOhm [4308R-101-564]	560 kOhm [4610X-101-564LF]
56.2 kOhm [CR0805-FX-5622ELF]	56.2 Ohm [CRM1206-FX-56R2ELF]	560 kOhm [4308R-101-564LF]	560 kOhm [4610X-102-564LF]
56.2 kOhm [CR1206-FX-5622ELF]	56.2 Ohm [CRT0402-FZ-56R2GLF]	560 kOhm [4308R-102-564]	560 kOhm [4816P-1-564]
56.2 kOhm [CRT0402-FZ-5622GLF]	56.2 Ohm [CRT1206-FZ-56R2ELF]	560 kOhm [4308R-102-564LF]	560 kOhm [4816P-1-564LF]
56.2 kOhm [CRT0603-BY-5622ELF]	560 kOhm [4114R-1-564]	560 kOhm [4310H-101-564]	560 kOhm [4816P-2-564]
56.2 kOhm [CRT1206-FZ-5622ELF]	560 kOhm [4114R-1-564LF]	560 kOhm [4310M-101-564]	560 kOhm [4816P-2-564LF]
56.2 Ohm [CAT16-56R2F4LF]	560 kOhm [4114R-2-564]	560 kOhm [4310M-101-564LF]	560 kOhm [4816P-T01-564]
	560 kOhm [4116R-1-564]	560 kOhm [4310R-101-564]	560 kOhm [4816P-T01-564LF]
		560 kOhm [4310R-101-564LF]	560 kOhm [4816P-T02-564]

Multisim 14.1 Base Edition Components

560 kOhm [4816P-T02-564LF]	560 kOhm [CR1206-FX-5603ELF]	560 mOhm [CRL2512-FW-R560ELF]	560 nF [C1206F564K4RACTU]
560 kOhm [CAT16-564J4LF]	560 kOhm [CR1206-JW-564ELF]	560 mOhm [PWR4318WR560JE]	560 nF [C1210C564K5RACTU]
560 kOhm [CAT25-564JALF]	560 kOhm [CRM2512-JW-564ELF]	560 mOhm [PWR4525WR560J]	560 nF [C1210F564K3RACTU]
560 kOhm [CAY10-564J4LF]	560 mOhm [CRL0603-FW-R560ELF]	560 mOhm [PWR4525WR560JE]	560 nF [C1210F564K4RACTU]
560 kOhm [CAY16-564J4LF]	560 mOhm [CRL0603-JW-R560ELF]	560 nF [C0603C564K8PACTU]	560 nF [C1210F564K5RACTU]
560 kOhm [CAY16-564J8LF]	560 mOhm [CRL0805-FW-R560ELF]	560 nF [C0805C564K3RACTU]	560 nF [C1812C564K5RACTU]
560 kOhm [CR0402-FX-5603GLF]	560 mOhm [CRL0805-JW-R560ELF]	560 nF [C0805C564K4RACTU]	560 nF [C1812F564K1RACTU]
560 kOhm [CR0402-JW-564GLF]	560 mOhm [CRL1206-FW-R560ELF]	560 nF [C0805C564K8RACTU]	560 nF [C1812F564K3RACTU]
560 kOhm [CR0603-FX-5603ELF]	560 mOhm [CRL1206-JW-R560ELF]	560 nF [C1206C564K3RACTU]	560 nF [C1812F564K5RACTU]
560 kOhm [CR0603-JW-564ELF]	560 mOhm [CRL2010-FW-R560ELF]	560 nF [C1206C564K4RACTU]	560 nF [C1825C564K5RACTU]
560 kOhm [CR0805-FX-5603ELF]	560 mOhm [CRL2010-JW-R560ELF]	560 nF [C1206C564K5RACTU]	560 nF [C1825C564KARACTU]

Multisim 14.1 Base Edition Components

560 nF [C2220C564K1RACT U]	560 nF [MDC15564K50B53 P3TUBE]	560 Ohm [4114R-1- 561]	560 Ohm [4308H- 101-561LF]
560 nF [C2220C564K5RACT U]	560 nF [MDK15564K100B5 3P3TUBE]	560 Ohm [4114R-1- 561LF]	560 Ohm [4308H- 102-561]
560 nF [C2220C564KARACT U]	560 nF [MDK15564K50B53 P3TUBE]	560 Ohm [4114R-2- 561]	560 Ohm [4308H- 102-561LF]
560 nF [C2225C564K5RACT U]	560 nH [SRP1038A- R56M]	560 Ohm [4116R-1- 561]	560 Ohm [4308R- 101-561]
560 nF [C2225C564KARACT U]	560 nH [SRP1040- R56M]	560 Ohm [4116R-1- 561LF]	560 Ohm [4308R- 101-561LF]
560 nF [MDC10564K100A5 2P3TUBE]	560 nH [SRP1250- R56M]	560 Ohm [4116R-2- 561]	560 Ohm [4308R- 102-561]
560 nF [MDC10564K250A5 4P3TUBE]	560 nH [SRP1265A- R56M]	560 Ohm [4116R-2- 561LF]	560 Ohm [4308R- 102-561LF]
560 nF [MDC10564K250A5 4P4TUBE]	560 nH [SRP4012- R56M]	560 Ohm [4306H- 102-561]	560 Ohm [4309R- 101-561]
560 nF [MDC10564K250A5 4P4TUBE]	560 nH [SRP4020- R56M]	560 Ohm [4306M- 101-561]	560 Ohm [4309R- 101-561LF]
560 nF [MDC10564K50A52 P3TUBE]	560 nH [SRP6540- R56M]	560 Ohm [4306R- 101-561]	560 Ohm [4310H- 101-561]
560 nF [MDC15564K100B5 3P3TUBE]	560 nH [SRP7028A- R56M]	560 Ohm [4306R- 101-561LF]	560 Ohm [4310H- 101-561LF]
560 nF [MDC15564K250B5 3P3TUBE]	560 nH [SRP7030- R56FM]	560 Ohm [4306R- 102-561]	560 Ohm [4310M- 101-561]
	560 nH [SRP7050TA-R56M]	560 Ohm [4306R- 102-561LF]	560 Ohm [4310M- 101-561LF]
		560 Ohm [4308H- 101-561]	560 Ohm [4310R- 101-561]

Multisim 14.1 Base Edition Components

560 Ohm [4310R-101-561LF]	560 Ohm [4607X-101-561LF]	560 Ohm [4816P-1-561]	560 Ohm [CAY10-561J4LF]
560 Ohm [4310R-102-561]	560 Ohm [4608M-102-561LF]	560 Ohm [4816P-1-561LF]	560 Ohm [CAY16-5600F4LF]
560 Ohm [4310R-102-561LF]	560 Ohm [4608X-101-561LF]	560 Ohm [4816P-2-561]	560 Ohm [CAY16-561J4LF]
560 Ohm [4416P-1-561]	560 Ohm [4608X-102-561LF]	560 Ohm [4816P-2-561LF]	560 Ohm [CAY16-561J8LF]
560 Ohm [4416P-1-561LF]	560 Ohm [4608X-AP2-561LF]	560 Ohm [4816P-T01-561]	560 Ohm [CAY17-561JALF]
560 Ohm [4416P-T01-561]	560 Ohm [4609X-101-561LF]	560 Ohm [4816P-T01-561LF]	560 Ohm [CR0402-FX-5600GLF]
560 Ohm [4420P-2-561]	560 Ohm [4610H-101-561LF]	560 Ohm [4816P-T02-561]	560 Ohm [CR0402-JW-561GLF]
560 Ohm [4420P-T02-561]	560 Ohm [4610X-101-561LF]	560 Ohm [4816P-T02-561LF]	560 Ohm [CR0603-FX-5600ELF]
560 Ohm [4604X-102-561LF]	560 Ohm [4610X-102-561LF]	560 Ohm [4820P-2-561]	560 Ohm [CR0603-FX-5600HLF]
560 Ohm [4605M-101-561LF]	560 Ohm [4610X-AP1-561LF]	560 Ohm [4820P-T01-561]	560 Ohm [CR0603-JW-561ELF]
560 Ohm [4605X-101-561LF]	560 Ohm [4612X-101-561LF]	560 Ohm [4820P-T02-561]	560 Ohm [CR0603-JW-561GLF]
560 Ohm [4606H-101-561LF]	560 Ohm [4612X-102-561LF]	560 Ohm [CAT16-5600F4LF]	560 Ohm [CR0805-FX-5600ELF]
560 Ohm [4606M-101-561LF]	560 Ohm [4814P-1-561]	560 Ohm [CAT16-561J4LF]	560 Ohm [CR0805-FX-5600GLF]
560 Ohm [4606X-101-561LF]	560 Ohm [4814P-T01-561]	560 Ohm [CAT16-561J8LF]	560 Ohm [CR0805-JW-561ELF]
560 Ohm [4606X-102-561LF]	560 Ohm [4814P-T01-561LF]	560 Ohm [CAT25-561JALF]	560 Ohm [CR0805-JW-561GLF]

Multisim 14.1 Base Edition Components

560 Ohm [CR1206-FX-5600ELF]	560 pF [C0402C561K4RACTU]	560 pF [C0603C561K5HACTU]	560 pF [C1206C561K2GACTU]
560 Ohm [CR1206-JW-561ELF]	560 pF [C0402C561K5HACTU]	560 pF [C0603C561K5RACTU]	560 pF [C1206C561K5GACTU]
560 Ohm [CR2010-JW-561ELF]	560 pF [C0402C561K5RACTU]	560 pF [C0603C561K8RACTU]	560 pF [C1206C561KBGAC TU]
560 Ohm [CR2512-JW-561ELF]	560 pF [C0402C561K8RACTU]	560 pF [C0805C561K1GACTU]	560 pF [C1210C561KBGAC TU]
560 Ohm [PWR163S-25-5600FE]	560 pF [C0603C561K1HACTU]	560 pF [C0805C561K1RACTU]	560 pF [C1812C561KBGAC TU]
560 Ohm [PWR221T-30-5600F]	560 pF [C0603C561K2RACTU]	560 pF [C0805C561K2RACTU]	560 pF [C1825C561KBGAC TU]
560 Ohm [PWR5322W5600FE]	560 pF [C0603C561K3HACTU]	560 pF [C0805C561K5GACTU]	560 pF [C2225C561KBGAC TU]
560 pF [C0402C561K1HACTU]	560 pF [C0603C561K3RACTU]	560 pF [C0805C561K5RACTU]	560 pF [CA064C561K2RACTU]
560 pF [C0402C561K3HACTU]	560 pF [C0603C561K4RACTU]	560 pF [C0805C561K8RACTU]	560 uF [16SVPF560M]
560 pF [C0402C561K3RACTU]	560 pF [C0603C561K5GACTU]	560 pF [C1206C561K1GACTU]	560 uF [2R5SVPC560M]
			560 uF [2SEPC560MW]

Multisim 14.1 Base Edition Components

560 uF [2SEPC560MZ]	560 uF [EEFLX0D561R4]	560 uH [SRR0745A- 561M]	560 uH [SRR5028- 561Y]
560 uF [4SEPC560M]	560 uF [EEFSX0D561E4]	560 uH [SRR0805- 561K]	560 uH [SRR7045- 561M]
560 uF [4SEPC560MW]	560 uF [T530D567M2R5AT E005]	560 uH [SRR0906- 561YL]	560 uH [SRU1048- 561Y]
560 uF [4SEPC560MX]	560 uH [SDE1006A- 561K]	560 uH [SRR0908- 561YL]	562 kOhm [CR0402-FX- 5623GLF]
560 uF [4SVP560M]	560 uH [SDR0302- 561KL]	560 uH [SRR1005- 561K]	562 kOhm [CR0603-FX- 5623ELF]
560 uF [4SVPC560M]	560 uH [SDR0403- 561KL]	560 uH [SRR1205- 561KL]	562 kOhm [CR0805-FX- 5623ELF]
560 uF [4SVPC560MX]	560 uH [SDR0503- 561KL]	560 uH [SRR1206- 561KL]	562 kOhm [CR1206-FX- 5623ELF]
560 uF [6SEPC560MW]	560 uH [SDR0604- 561KL]	560 uH [SRR1208- 561KL]	562 kOhm [CR1206-FX- 5623ELF]
560 uF [6SEPC560MX]	560 uH [SDR0703- 561KL]	560 uH [SRR1210- 561M]	562 Ohm [CAY16- 5620F4LF]
560 uF [EEFCX0D561R]	560 uH [SDR0805- 561KL]	560 uH [SRR1210A- 561M]	562 Ohm [CR0402- FX-5620GLF]
560 uF [EEFGX0D561L]	560 uH [SDR0906- 561KL]	560 uH [SRR1240- 561K]	562 Ohm [CR0603- FX-5620ELF]
560 uF [EEFGX0D561R]	560 uH [SDR1006- 561KL]	560 uH [SRR1260- 561K]	562 Ohm [CR0603- FX-5620GLF]
560 uF [EEFHX0D561R]	560 uH [SDR1307- 561KL]	560 uH [SRR1260A- 561K]	562 Ohm [CR0805- FX-5620ELF]
560 uF [EEFHX0D561R4]	560 uH [SDR1307A-561K]	560 uH [SRR1280- 561K]	562 Ohm [CR1206- FX-5620ELF]
560 uF [EEFLX0D561R]	560 uH [SRR0735A- 561M]	560 uH [SRR4028- 561Y]	

Multisim 14.1 Base Edition Components

562 Ohm [CRM1206-FX- 5620ELF]	571-0500	59 kOhm [CR1206- FX-5902ELF]	590 Ohm [CR0603- FX-5900ELF]
562 Ohm [CRT0402-FZ- 5620GLF]	571-0600	59 kOhm [CRM2010-FX- 5902ELF]	590 Ohm [CR0805- FX-5900ELF]
562 Ohm [CRT1206-FZ- 5620ELF]	571-0700	59 Ohm [CR0402- FX-59R0GLF]	590 Ohm [CR1206- FX-5900ELF]
5687169-9	576 kOhm [CR0402-FX- 5763GLF]	59 Ohm [CR0603- FX-59R0ELF]	5KP10A-E3/54
57.6 kOhm [CR0402-FX- 5762GLF]	576 kOhm [CR0603-FX- 5763ELF]	59 Ohm [CR0805- FX-59R0ELF]	5KP16A-E3/54
57.6 kOhm [CR0603-FX- 5762ELF]	576 kOhm [CR0805-FX- 5763ELF]	59 Ohm [CR1206- FX-59R0ELF]	5KP18A-E3/54
57.6 kOhm [CR0805-FX- 5762ELF]	576 Ohm [CR0402- FX-5760GLF]	59 Ohm [CRM2512-FX- 59R0ELF]	5KP22A-E3/54
57.6 kOhm [CR1206-FX- 5762ELF]	576 Ohm [CR0603- FX-5760ELF]	59 Ohm [CRT0402- FZ-59R0GLF]	5KP24A-E3/54
57.6 Ohm [CR0603- FX-57R6ELF]	576 Ohm [CR0805- FX-5760ELF]	590 kOhm [CR0402-FX- 5903GLF]	5KP28A-E3/54
57.6 Ohm [CR0805- FX-57R6ELF]	576 Ohm [CR1206- FX-5760ELF]	590 kOhm [CR0603-FX- 5903ELF]	5KP30A-E3/54
57.6 Ohm [CR1206- FX-57R6ELF]	59 kOhm [CR0402- FX-5902GLF]	590 kOhm [CR0805-FX- 5903ELF]	5KP33A-E3/54
571-0100	59 kOhm [CR0603- FX-5902ELF]	590 kOhm [CR1206-FX- 5903ELF]	5KP40A-E3/54
571-0200	59 kOhm [CR0805- FX-5902ELF]	590 Ohm [CR0402- FX-5900GLF]	5KP48A-E3/54
571-0300	59 kOhm [CR1206- FX-5902ELF]		5KP58A-E3/54
571-0400			5KP60A-E3/54
			5KP85A-E3/54
			5Line_Bussed
			5Line_Isolated
			5LN01C-TB-E
			5LN01C-TB-H
			5LN01M-TL-E
			5LN01M-TL-H
			5LN01SP-AC

Multisim 14.1 Base Edition Components

5LN01SS-TL-E	6 mOhm	6.04 kOhm	6.19 kOhm
5LN01SS-TL-H	[PWR4412-2SBR0060F]	[CRT0603-BY-6041ELF]	[CRT0805-CX-6191ELF]
5LN01S-TL-E	6 Ohm [PWR221T-50-6R00F]	6.04 kOhm	6.2 kOhm [4114R-2-622]
5LP01C-TB-E		[CRT0805-FZ-6041ELF]	
5LP01C-TB-H	6 Ohm	6.04 Ohm	6.2 kOhm [4114R-2-622LF]
5LP01M-TL-E	[PWR4525W6R00F]	[CRT0805-BY-6R04ELF]	
5LP01M-TL-H	6 Ohm		6.2 kOhm [4116R-2-622]
5LP01SP	[PWR4525W6R00F E]	6.1 uH [SRR1260-6R1Y]	6.2 kOhm [4309R-101-622]
5LP01SP-AC	6 uH [SRN6028-6R0M]	6.1 uH [SRR1260A-6R1Y]	6.2 kOhm [4309R-101-622LF]
5LP01SS-TL-E	6 uH [SRP1250-6R0M]	6.1 uH [SRR1280-6R1Y]	6.2 kOhm [4310R-101-622]
5LP01SS-TL-H			
5LP01S-TL-E	6 uH [SRR6028-6R0Y]	6.19 kOhm	6.2 kOhm [4604X-101-622LF]
5POS_ROTARY	6 uH [SRU2016-6R0Y]	[CR0402-FX-6191GLF]	
5V_1W		6.19 kOhm	6.2 kOhm [4609X-101-622LF]
6 kOhm [4116R-1-602]	6.04 kOhm [CAY16-6041F4LF]	[CR0603-FX-6191ELF]	6.2 kOhm [4814P-1-622LF]
6 kOhm [4116R-1-602LF]	6.04 kOhm	6.19 kOhm	6.2 kOhm [4816P-1-622]
6 kOhm [4116R-2-602]	[CR0402-FX-6041GLF]	[CR0805-FX-6191ELF]	
	6.04 kOhm	6.19 kOhm	6.2 kOhm [4816P-1-622LF]
6 mOhm [CRE2512-FZ-R006E-2]	[CR0603-FX-6041ELF]	[CR0805-FX-6191GLF]	
6 mOhm [CRE2512-FZ-R006E-3]	6.04 kOhm	6.19 kOhm	6.2 kOhm [4816P-T02-622]
	[CR0805-FX-6041ELF]	[CR1206-FX-6191ELF]	6.2 kOhm [CAY16-622J4LF]
6 mOhm [CRF2512-FX-R006ELF]	6.04 kOhm	6.19 kOhm	6.2 kOhm [CR0402-FX-6201GLF]
	[CR1206-FX-6041ELF]	[CRT0402-FZ-6191GLF]	

Multisim 14.1 Base Edition Components

6.2 kOhm [CR0402-JW-622GLF]	6.2 nF [C0603C622K3HACT U]	6.2 Ohm [CRL0805-FW-6R20ELF]	6.2 uH [SRU1038-6R2Y]
6.2 kOhm [CR0603-FX-6201ELF]	6.2 nF [C0603C622K5HACT U]	6.2 Ohm [CRL1206-FW-6R20ELF]	6.2 uH [SRU1038A-6R2Y]
6.2 kOhm [CR0603-JW-622ELF]	6.2 nF [C0805C622K1GACT U]	6.2 Ohm [CRL2010-FW-6R20ELF]	6.3 uH [SRR7045-6R3M]
6.2 kOhm [CR0805-FX-6201ELF]	6.2 nF [C0805C622K1HACT U]	6.2 Ohm [CRL2010-JW-6R20ELF]	6.34 kOhm [CR0402-FX-6341GLF]
6.2 kOhm [CR0805-JW-622ELF]	6.2 nF [C0805C622K3HACT U]	6.2 Ohm [CRL2512-FW-6R20ELF]	6.34 kOhm [CR0603-FX-6341ELF]
6.2 kOhm [CR1206-FX-6201ELF]	6.2 nF [C0805C622K3HACT U]	6.2 Ohm [CRM2512-JW-6R2ELF]	6.34 kOhm [CR0805-FX-6341ELF]
6.2 kOhm [CR1206-JW-622ELF]	6.2 nF [C0805C622K5HACT U]	6.2 Ohm [FW10A6R20JA]	6.34 kOhm [CR1206-FX-6341ELF]
6.2 MOhm [4116R-1-625]	6.2 nF [C2225C622KBGAC TU]	6.2 Ohm [PWR263S-20-6R20FE]	6.34 kOhm [CRT0603-BW-6341ELF]
6.2 MOhm [4116R-1-625LF]	6.2 Ohm [CR0402-J/-6R2GLF]	6.2 uH [SDR7030-6R2M]	6.34 kOhm [CRT0603-DV-6341ELF]
6.2 MOhm [CR0603-JW-625ELF]	6.2 Ohm [CR0603-J/-6R2ELF]	6.2 uH [SRN6028-6R2M]	6.49 kOhm [CR0402-FX-6491GLF]
6.2 MOhm [CR0805-FX-6204ELF]	6.2 Ohm [CR1206-J/-6R2ELF]	6.2 uH [SRR4011-6R2YL]	6.49 kOhm [CR0603-FX-6491ELF]
6.2 MOhm [CR0805-JW-625ELF]	6.2 Ohm [CRL0603-FW-6R20ELF]	6.2 uH [SRR5018-6R2Y]	6.49 kOhm [CR0805-FX-6491ELF]
6.2 MOhm [CR1206-JW-625ELF]	6.2 Ohm [CRL0603-JW-6R20ELF]	6.2 uH [SRR5028-6R2Y]	
		6.2 uH [SRR6038-6R2Y]	

Multisim 14.1 Base Edition Components

6.49 kOhm [CR1206-FX- 6491ELF]	6.8 kOhm [4116R- 1-682LF]	6.8 kOhm [4308M- 102-682LF]	6.8 kOhm [4310R- 102-682]
6.49 kOhm [CRT0603-BY- 6491ELF]	6.8 kOhm [4116R- 2-682]	6.8 kOhm [4308R- 101-682]	6.8 kOhm [4310R- 102-682LF]
6.5 uH [SRR1208- 6R5ML]	6.8 kOhm [4116R- 2-682LF]	6.8 kOhm [4308R- 101-682LF]	6.8 kOhm [4604X- 101-682LF]
6.65 kOhm [CR0402-FX- 6651GLF]	6.8 kOhm [4304M- 101-682]	6.8 kOhm [4308R- 102-682]	6.8 kOhm [4604X- 102-682LF]
6.65 kOhm [CR0402-FX- 6651GLF]	6.8 kOhm [4306M- 101-682]	6.8 kOhm [4308R- 102-682LF]	6.8 kOhm [4605X- 101-682LF]
6.65 kOhm [CR0603-FX- 6651ELF]	6.8 kOhm [4306M- 101-682LF]	6.8 kOhm [4309R- 101-682]	6.8 kOhm [4606X- 101-682LF]
6.65 kOhm [CR0603-FX- 6651ELF]	6.8 kOhm [4306R- 101-682]	6.8 kOhm [4309R- 101-682LF]	6.8 kOhm [4606X- 102-682LF]
6.65 kOhm [CR0805-FX- 6651ELF]	6.8 kOhm [4306R- 101-682LF]	6.8 kOhm [4310H- 101-682]	6.8 kOhm [4606X- AP2-682LF]
6.65 kOhm [CR1206-FX- 6651ELF]	6.8 kOhm [4306R- 102-682]	6.8 kOhm [4310H- 101-682LF]	6.8 kOhm [4607X- 101-682LF]
6.8 kOhm [4108R- 1-682LF]	6.8 kOhm [4306R- 102-682LF]	6.8 kOhm [4310H- 102-682]	6.8 kOhm [4608M- 102-682LF]
6.8 kOhm [4114R- 1-682]	6.8 kOhm [4308H- 102-682]	6.8 kOhm [4310H- 102-682LF]	6.8 kOhm [4608X- 101-682LF]
6.8 kOhm [4114R- 1-682LF]	6.8 kOhm [4308H- 102-682LF]	6.8 kOhm [4310M- 101-682]	6.8 kOhm [4608X- 102-682LF]
6.8 kOhm [4114R- 2-682]	6.8 kOhm [4308M- 101-682]	6.8 kOhm [4310M- 101-682LF]	6.8 kOhm [4608X- AP1-682LF]
6.8 kOhm [4114R- 2-682LF]	6.8 kOhm [4308M- 101-682LF]	6.8 kOhm [4310R- 101-682]	6.8 kOhm [4608X- AP2-682LF]
6.8 kOhm [4116R- 1-682]	6.8 kOhm [4308M- 102-682]	6.8 kOhm [4310R- 101-682LF]	6.8 kOhm [4609H- 101-682LF]

Multisim 14.1 Base Edition Components

6.8 kOhm [4609M-101-682LF]	6.8 kOhm [4816P-1-682]	6.8 kOhm [CAT16-682J2LF]	6.8 kOhm [CR0603-JW-682GLF]
6.8 kOhm [4609X-101-682LF]	6.8 kOhm [4816P-1-682LF]	6.8 kOhm [CAT16-682J4LF]	6.8 kOhm [CR0805-FX-6801ELF]
6.8 kOhm [4609X-AP1-682LF]	6.8 kOhm [4816P-2-682]	6.8 kOhm [CAT16-682J8LF]	6.8 kOhm [CR0805-JW-682ELF]
6.8 kOhm [4610H-101-682LF]	6.8 kOhm [4816P-2-682LF]	6.8 kOhm [CAT25-682JALF]	6.8 kOhm [CR1206-FX-6801ELF]
6.8 kOhm [4610M-101-682LF]	6.8 kOhm [4816P-T01-682]	6.8 kOhm [CAY10-682J4LF]	6.8 kOhm [CR1206-JW-682ELF]
6.8 kOhm [4610X-101-682LF]	6.8 kOhm [4816P-T01-682LF]	6.8 kOhm [CAY16-6801F4LF]	6.8 kOhm [CR1206-JW-682GLF]
6.8 kOhm [4610X-102-682LF]	6.8 kOhm [4816P-T02-682]	6.8 kOhm [CAY16-682J4LF]	6.8 kOhm [CR2512-FX-6801ELF]
6.8 kOhm [4611X-101-682LF]	6.8 kOhm [4816P-T02-682LF]	6.8 kOhm [CAY16-682J8LF]	6.8 kOhm [CR2512-JW-682ELF]
6.8 kOhm [4612X-102-682LF]	6.8 kOhm [4818P-2-682]	6.8 kOhm [CAY17-682JALF]	6.8 kOhm [CRM1206-FX-6801ELF]
6.8 kOhm [4814P-2-682]	6.8 kOhm [4818P-T02-682]	6.8 kOhm [CR0201-FW-6801GLF]	6.8 kOhm [CRM1206-JW-682ELF]
6.8 kOhm [4814P-2-682LF]	6.8 kOhm [4820P-1-682]	6.8 kOhm [CR0201-JW-682GLF]	6.8 kOhm [CRM2010-JW-682ELF]
6.8 kOhm [4814P-T01-682]	6.8 kOhm [4820P-2-682]	6.8 kOhm [CR0402-FX-6801GLF]	6.8 kOhm [CRM2512-FX-6801ELF]
6.8 kOhm [4814P-T01-682LF]	6.8 kOhm [4820P-T02-682]	6.8 kOhm [CR0402-JW-682GLF]	6.8 kOhm [CRM2512-JW-682ELF]
6.8 kOhm [4814P-T02-682]	6.8 kOhm [CAT10-682J4LF]	6.8 kOhm [CR0603-FX-6801ELF]	6.8 kOhm [CRM2512-JW-682ELF]
6.8 kOhm [4814P-T02-682LF]	6.8 kOhm [CAT16-6801F4LF]	6.8 kOhm [CR0603-JW-682ELF]	

Multisim 14.1 Base Edition Components

6.8 kOhm [CRT0805-BY-6801ELF]	6.8 MOhm [4116R-1-685]	6.8 nF [C0603C682K2RACTU]	6.8 nF [C0805C682K3GACTU]
6.8 kOhm [CRT0805-DY-6801ELF]	6.8 MOhm [4116R-1-685LF]	6.8 nF [C0603C682K3GACTU]	6.8 nF [C0805C682K3HACTU]
6.8 kOhm [PWR4525W6801J]	6.8 MOhm [CAT25-685JALF]	6.8 nF [C0603C682K3HACTU]	6.8 nF [C0805C682K3RACTU]
6.8 kOhm [PWR4525W6801JE]	6.8 MOhm [CHV2512-JW-685ELF]	6.8 nF [C0603C682K3RACTU]	6.8 nF [C0805C682K4RACTU]
6.8 kOhm [PWR6327W6801J]	6.8 MOhm [CR0603-JW-685ELF]	6.8 nF [C0603C682K4RACTU]	6.8 nF [C0805C682K5GACTU]
6.8 kOhm [PWR6327W6801JE]	6.8 MOhm [CR0805-JW-685ELF]	6.8 nF [C0603C682K5HACTU]	6.8 nF [C0805C682K5HACTU]
6.8 mH [SDR0503-682JL]	6.8 MOhm [CR1206-JW-685ELF]	6.8 nF [C0603C682K5RACTU]	6.8 nF [C0805C682K5RACTU]
6.8 mH [SDR0906-682KL]	6.8 nF [C0402C682K3RACTU]	6.8 nF [C0603C682K8RACTU]	6.8 nF [C1206C682K1HACTU]
6.8 mH [SDR1005-682KL]	6.8 nF [C0402C682K4RACTU]	6.8 nF [C0805C682K1GACTU]	6.8 nF [C1206C682K1RACTU]
6.8 mH [SRE6603-682M]	6.8 nF [C0402C682K5RACTU]	6.8 nF [C0805C682K1HACTU]	6.8 nF [C1206C682K3GACTU]
6.8 mH [SRR0906-682YL]	6.8 nF [C0402C682K8RACTU]	6.8 nF [C0805C682K1RACTU]	6.8 nF [C1206C682K3HACTU]
6.8 mH [SRR0908-682YL]	6.8 nF [C0603C682K1RACTU]		
6.8 mH [SRR1208-682KL]			
6.8 mH [SRR6603-682ML]			

Multisim 14.1 Base Edition Components

6.8 nF [C1206C682K3RACT U]	6.8 nF [C1812C682K5RACT U]	6.8 nF [GPC7.3681K630K3 1TR12]	6.8 nF [SPC10.2682K100A 31TR16]
6.8 nF [C1206C682K5HACT U]	6.8 nF [C2220C682K2GACT U]	6.8 nF [GPC7.3682K160K3 1TR12]	6.8 nF [SPC10.2682K250A 31TR16]
6.8 nF [C1206C682K5RACT U]	6.8 nF [C2225C682KBGAC TU]	6.8 nF [GPC7.3682K63K31 TR12]	6.8 nF [SPC10.2682K400A 31TR16]
6.8 nF [C1210C682K1GACT U]	6.8 nF [CDR06BP682BKSM]	6.8 nF [MMC5.7682K100J 31TR12]	6.8 nF [SPC10.2682K630A 31TR16]
6.8 nF [C1210C682K1RACT U]	6.8 nF [GMC5.7682K100J3 1TR12]	6.8 nF [MMC5.7682K250J 31TR12]	6.8 nF [SPC7.3682K100K31 TR12]
6.8 nF [C1210C682K5GACT U]	6.8 nF [GMC5.7682K250J3 1TR12]	6.8 nF [MMC5.7682K50J3 1TR12]	6.8 nF [SPC7.3682K250K33 TR12]
6.8 nF [C1210C682K5RACT U]	6.8 nF [GMC5.7682K50J31 TR12]	6.8 nF [MMC7.3682K100K 31TR12]	6.8 nF [SPC7.3682K400K37 TR12]
6.8 nF [C1210C682KARACT U]	6.8 nF [GMC7.3682K100K3 1TR12]	6.8 nF [MMC7.3682K250K 31TR12]	6.8 Ohm [CR0402- J/-6R8GLF]
6.8 nF [C1812C682K1GACT U]	6.8 nF [GMC7.3682K400K3 3TR12]	6.8 nF [MMC7.3682K400K 33TR12]	6.8 Ohm [CR0603- J/-6R8ELF]
6.8 nF [C1812C682K1RACT U]	6.8 nF [GMC7.3682K63K31 TR12]	6.8 nF [MMC7.3682K50K3 1TR12]	6.8 Ohm [CR0603- J/-6R8GLF]
6.8 nF [C1812C682K5GACT U]	6.8 nF [GMC7.3683K100K3 5TR12]	6.8 nF [MMC7.3682K63K3 1TR12]	6.8 Ohm [CR0805- J/-6R8ELF]
			6.8 Ohm [CR1206- J/-6R8ELF]
			6.8 Ohm [CR2512- J/-6R8ELF]

Multisim 14.1 Base Edition Components

6.8 Ohm [CRL0603-FW-6R80ELF]	6.8 Ohm [FW70A6R80JA]	6.8 uF [C1210C685K4PACT U]	6.8 uF [T419C685M010AH 4250]
6.8 Ohm [CRL0603-JW-6R80ELF]	6.8 Ohm [PWR2615W6R80F E]	6.8 uF [C1210C685K8PACT U]	6.8 uF [T429D685M006AH 4250]
6.8 Ohm [CRL0805-FW-6R80ELF]	6.8 uF [A700V685M016AT E070]	6.8 uF [C1210C685M4VAC TU]	6.8 uF [T489B685M010AT E3K0]
6.8 Ohm [CRL0805-JW-6R80ELF]	6.8 uF [C0805C685K8PACT U]	6.8 uF [MDC10685K100A5 7P7TUBE]	6.8 uF [T491A685M004AT]
6.8 Ohm [CRL1206-FW-6R80ELF]	6.8 uF [C0805C685K9PACT U]	6.8 uF [MDC10685K100A5 7P8TUBE]	6.8 uF [T491A685M006AT]
6.8 Ohm [CRL1206-JW-6R80ELF]	6.8 uF [C1206C685K4PACT U]	6.8 uF [MDC10685K50A55 P3TUBE]	6.8 uF [T491A685M016AT]
6.8 Ohm [CRL2010-FW-6R80ELF]	6.8 uF [C1206C685K4RACT U]	6.8 uF [MDC10685K50A55 P4TUBE]	6.8 uF [T491A685M020AT]
6.8 Ohm [CRL2010-JW-6R80ELF]	6.8 uF [C1206C685K8RACT U]	6.8 uF [MDC10685K50A55 P5TUBE]	6.8 uF [T491B685M006AT]
6.8 Ohm [CRM2512-FX-6R80ELF]	6.8 uF [C1206C685K9PACT U]	6.8 uF [MDC15685K50B53 P3TUBE]	6.8 uF [T491B685M010AT]
6.8 Ohm [CRM2512-JW-6R8ELF]	6.8 uF [C1206C685K9RACT U]	6.8 uF [MMC16.5685K50C 31TR24]	6.8 uF [T491B685M025AT]
6.8 Ohm [FW10A6R80JA]	6.8 uF [C1210C685K3PACT U]	6.8 uF [T419B685M006AH 4250]	6.8 uF [T491C685M016AT]
6.8 Ohm [FW20A6R80JA]			6.8 uF [T491C685M020AT]
6.8 Ohm [FW30A6R80JA]			
6.8 Ohm [FW50A6R80JA]			

Multisim 14.1 Base Edition Components

6.8 uF [T491C685M025AT]	6.8 uF [T494A685M020AT]	6.8 uF [T494T685M010AT]	6.8 uF [T498D685M035AT E900]
6.8 uF [T491C685M035AT]	6.8 uF [T494B685M006AT]	6.8 uF [T494U685M020AT]	6.8 uF [T499C685M020AT E1K9]
6.8 uF [T491D685M035AT]	6.8 uF [T494B685M010AT]	6.8 uF [T494X685M050AT]	6.8 uF [T521D685M050AT E090]
6.8 uF [T491D685M050AT]	6.8 uF [T494B685M016AT]	6.8 uF [T495C685M025AT E400]	6.8 uF [T521V685M050AT E090]
6.8 uF [T491S685M004AT]	6.8 uF [T494B685M025AT]	6.8 uF [T495C685M025AT E500]	6.8 uF [TACL685K002RTA]
6.8 uF [T491S685M006AT]	6.8 uF [T494C685M016AT]	6.8 uF [T495D685M035AT E150]	6.8 uF [TACL685K003RTA]
6.8 uF [T491S685M010AT]	6.8 uF [T494C685M020AT]	6.8 uF [T495D685M050AT E190]	6.8 uF [TACL685K004RTA]
6.8 uF [T491T685M010AT]	6.8 uF [T494C685M025AT]	6.8 uF [T495D685M050AT E200]	6.8 uF [TACR685K006RTA]
6.8 uF [T491U685M020AT]	6.8 uF [T494C685M035AT]	6.8 uF [T495D685M050AT E300]	6.8 uF [TAJA685K006RNJ]
6.8 uF [T491X685M050AT]	6.8 uF [T494D685M035AT]	6.8 uF [T497B685M010AT 6110]	6.8 uF [TAJA685K010RNJ]
6.8 uF [T494A685M004AT]	6.8 uF [T494D685M050AT]	6.8 uF [T498A685M016AT E2K6]	6.8 uF [TAJA685K020RNJ]
6.8 uF [T494A685M006AT]	6.8 uF [T494S685M004AT]	6.8 uF [T498B685M016AT E1K8]	
6.8 uF [T494A685M010AT]	6.8 uF [T494S685M006AT]		
6.8 uF [T494A685M016AT]	6.8 uF [T494S685M010AT]		

Multisim 14.1 Base Edition Components

6.8 uF [TAJB685K010RNJ]	6.8 uF [TAJS685K004RNJ]	6.8 uF [TPSA685K016R150 0]	6.8 uF [TPSD685K050R060 0]
6.8 uF [TAJB685K016RNJ]	6.8 uF [TAJS685K010RNJ]	6.8 uF [TPSB685K016R120 0]	6.8 uF [TPST685K010R180 0]
6.8 uF [TAJB685K020RNJ]	6.8 uF [TAJT685K004RNJ]	6.8 uF [TPSB685K020R100 0]	6.8 uF [TRJA685K016RRJ]
6.8 uF [TAJB685K025RNJ]	6.8 uF [TAJT685K006RNJ]	6.8 uF [TPSC685K020R070 0]	6.8 uF [TRJB685K025RRJ]
6.8 uF [TAJC685K016RNJ]	6.8 uF [TAJT685K010RNJ]	6.8 uF [TPSC685K020R070 0]	6.8 uF [TRJD685K050RRJ]
6.8 uF [TAJC685K020RNJ]	6.8 uF [TAJT685K016RNJ]	6.8 uF [TPSC685K025R050 0]	6.8 uH [SDE0403A- 6R8M]
6.8 uF [TAJC685K025RNJ]	6.8 uF [TAJT685K020RNJ]	6.8 uF [TPSC685K025R060 0]	6.8 uH [SDE0604A- 6R8M]
6.8 uF [TAJC685K035RNJ]	6.8 uF [TAJW685K025RNJ]	6.8 uF [TPSC685K025R070 0]	6.8 uH [SDE0805A- 6R8M]
6.8 uF [TAJD685K050RNJ]	6.8 uF [THJA685K016RJN]	6.8 uF [TPSC685K025R070 0]	6.8 uH [SDE1006A- 6R8M]
6.8 uF [TAJD685K035RNJ]	6.8 uF [THJB685K016RJN]	6.8 uF [TPSD685K035R015 0]	6.8 uH [SDR0302- 6R8ML]
6.8 uF [TAJD685K050RNJ]	6.8 uF [THJC685K025RJN]	6.8 uF [TPSD685K035R040 0]	6.8 uH [SDR0403- 6R8ML]
6.8 uF [TAJP685K010RNJ]	6.8 uF [THJD685K035RJN]	6.8 uF [TPSD685K035R050 0]	6.8 uH [SDR0603- 6R8ML]
6.8 uF [TAJR685K002RNJ]	6.8 uF [TPSA685K006R180 0]	6.8 uF [TPSD685K035R050 0]	6.8 uH [SDR0604- 6R8ML]
6.8 uF [TAJR685K006RNJ]	6.8 uF [TPSA685K010R180 0]	6.8 uF [TPSD685K050R050 0]	6.8 uH [SDR0703- 6R8ML]
6.8 uF [TAJR685K010RNJ]			6.8 uH [SDR0805- 6R8ML]

Multisim 14.1 Base Edition Components

6.8 uH [SDR0906-6R8ML]	6.8 uH [SRN5020-6R8M]	6.8 uH [SRP5015TA-6R8M]	6.8 uH [SRR1260A-6R8Y]
6.8 uH [SDR1005-6R8ML]	6.8 uH [SRN5040-6R8M]	6.8 uH [SRP5030T-6R8M]	6.8 uH [SRR1280-6R8Y]
6.8 uH [SDR1006-6R8ML]	6.8 uH [SRN6028-6R8M]	6.8 uH [SRP5030TA-6R8M]	6.8 uH [SRR3011-6R8YL]
6.8 uH [SDR1030-6R8M]	6.8 uH [SRN6045-6R8Y]	6.8 uH [SRP6540-6R8M]	6.8 uH [SRR4018-6R8Y]
6.8 uH [SDR1045-6R8M]	6.8 uH [SRN8040-6R8Y]	6.8 uH [SRP7028A-6R8M]	6.8 uH [SRR4028-6R8Y]
6.8 uH [SDR1305-6R8Y]	6.8 uH [SRP1038A-6R8M]	6.8 uH [SRP7030-6R8FM]	6.8 uH [SRR6040A-6R8Y]
6.8 uH [SDR1307-6R8ML]	6.8 uH [SRP1040-6R8M]	6.8 uH [SRR0603-6R8ML]	6.8 uH [SRR6603-6R8ML]
6.8 uH [SDR1307A-6R8M]	6.8 uH [SRP1235-6R8M]	6.8 uH [SRR0604-6R8ML]	6.8 uH [SRR7032-6R8M]
6.8 uH [SDR6603-6R8M]	6.8 uH [SRP1245A-6R8M]	6.8 uH [SRR0618-6R8ML]	6.8 uH [SRR7045-6R8M]
6.8 uH [SDR7045-6R8M]	6.8 uH [SRP1250-6R8M]	6.8 uH [SRR0906-6R8ML]	6.8 uH [SRU1028-6R8Y]
6.8 uH [SRN3010-6R8M]	6.8 uH [SRP1265A-6R8M]	6.8 uH [SRR1005-6R8M]	6.8 uH [SRU1028A-6R8Y]
6.8 uH [SRN3015-6R8M]	6.8 uH [SRP1270-6R8M]	6.8 uH [SRR1210-6R8Y]	6.8 uH [SRU1038-6R8Y]
6.8 uH [SRN4012T-6R8M]	6.8 uH [SRP1770TA-6R8M]	6.8 uH [SRR1210A-6R8Y]	6.8 uH [SRU1048-6R8Y]
6.8 uH [SRN4018-6R8M]	6.8 uH [SRP4012TA-6R8M]	6.8 uH [SRR1240-6R8M]	6.8 uH [SRU1048A-6R8Y]
6.8 uH [SRN4026-6R8M]	6.8 uH [SRP4020TA-6R8M]	6.8 uH [SRR1260-6R8Y]	6.8 uH [SRU2009-6R8Y]

Multisim 14.1 Base Edition Components

6.8 uH [SRU2011-6R8Y]	6.8 uH [SRU8028A-6R8Y]	6.9 kOhm [4116R-1-692]	60.4 kOhm [CR0805-FX-6042ELF]
6.8 uH [SRU2013-6R8Y]	6.8 uH [SRU8043-6R8Y]	6.98 kOhm [CR0402-FX-6981GLF]	60.4 kOhm [CR1206-FX-6042ELF]
6.8 uH [SRU3011-6R8Y]	6.81 kOhm [CAT16-6811F4LF]	6.98 kOhm [CR0603-FX-6981ELF]	60.4 kOhm [CRT0805-BY-6042ELF]
6.8 uH [SRU3014-6R8Y]	6.81 kOhm [CR0402-FX-6811GLF]	6.98 kOhm [CR0805-FX-6981ELF]	60.4 Ohm [CAY16-60R4F4LF]
6.8 uH [SRU3017-6R8Y]	6.81 kOhm [CR0603-FX-6811ELF]	6.98 kOhm [CR1206-FX-6981ELF]	60.4 Ohm [CR0201-FW-60R4GLF]
6.8 uH [SRU5011-6R8Y]	6.81 kOhm [CR0805-FX-6811ELF]	6.98 kOhm [CRT0805-BY-6981ELF]	60.4 Ohm [CR0402-FX-60R4GLF]
6.8 uH [SRU5016-6R8Y]	6.81 kOhm [CR1206-FX-6811ELF]	60 mOhm [CRA2512-FZ-R060ELF]	60.4 Ohm [CR0805-FX-60R4ELF]
6.8 uH [SRU5018-6R8Y]	6.81 kOhm [CRT0402-FZ-6811GLF]	60 mOhm [CRA2512-JZ-R060ELF]	60.4 Ohm [CR1206-FX-60R4ELF]
6.8 uH [SRU5028-6R8Y]	6.81 kOhm [CRT0603-BY-6811ELF]	60 mOhm [CRL0805-FW-R060ELF]	60.4 Ohm [CRM2512-FX-60R4ELF]
6.8 uH [SRU5028A-6R8Y]	6.81 kOhm [CRT0805-BY-6811ELF]	60.4 kOhm [CAT16-6042F8LF]	60.4 Ohm [CRT0805-BY-60R4ELF]
6.8 uH [SRU6011-6R8Y]	6.81 kOhm [CRT1206-FZ-6811ELF]	60.4 kOhm [CR0402-FX-6042GLF]	600 mOhm [PWR4318WR600F]
6.8 uH [SRU6018-6R8Y]	6.81 Ohm [CRM1206-FX-6R81ELF]	60.4 kOhm [CR0603-FX-6042ELF]	600 nH [SRP1235-R60M]

Multisim 14.1 Base Edition Components

600 nH [SRP4012TA-R60M]	604 Ohm [CR1206- FX-6040ELF]	61.9 Ohm [CRT0402-FZ- 61R9GLF]	62 kOhm [4114R-2- 623]
600 nH [SRP7050TA-R60M]	61.9 kOhm [CR0201-FW- 6192GLF]	61.9 Ohm [CRT0805-FY- 61R9ELF]	62 kOhm [4114R-2- 623LF]
604 kOhm [CAT16- 6043F8LF]	61.9 kOhm [CR0402-FX- 6192GLF]	61729-0010BLF	62 kOhm [4310R- 102-623]
604 kOhm [CR0402-FX- 6043GLF]	61.9 kOhm [CR0603-FX- 6192ELF]	619 kOhm [CR0402-FX- 6193GLF]	62 kOhm [CAT16- 6202F4LF]
604 kOhm [CR0603-FX- 6043ELF]	61.9 kOhm [CR0805-FX- 6192ELF]	619 kOhm [CR0603-FX- 6193ELF]	62 kOhm [CAY16- 6202F4LF]
604 kOhm [CR0805-FX- 6043ELF]	61.9 kOhm [CR1206-FX- 6192ELF]	619 kOhm [CR0805-FX- 6193ELF]	62 kOhm [CAY16- 623J4LF]
604 kOhm [CR1206-FX- 6043ELF]	61.9 kOhm [CRT0603-BY- 6192ELF]	619 kOhm [CR1206-FX- 6193ELF]	62 kOhm [CAY17- 623JALF]
604 kOhm [CRM2512-FX- 6043ELF]	61.9 kOhm [CRT0805-CX- 6192ELF]	619 Ohm [CR0402- FX-6190GLF]	62 kOhm [CR0201- FW-6202GLF]
604 kOhm [CRT0805-BY- 6043ELF]	61.9 Ohm [CAT16- 61R9F8LF]	619 Ohm [CR0603- FX-6190ELF]	62 kOhm [CR0402- FX-6202GLF]
604 Ohm [CAY16- 6040F4LF]	61.9 Ohm [CR0402- FX-61R9GLF]	619 Ohm [CR0805- FX-6190ELF]	62 kOhm [CR0402- JW-623GLF]
604 Ohm [CR0402- FX-6040GLF]	61.9 Ohm [CR0603- FX-61R9ELF]	619 Ohm [CR0805- FX-6190GLF]	62 kOhm [CR0603- FX-6202ELF]
604 Ohm [CR0603- FX-6040ELF]	61.9 Ohm [CR0805- FX-61R9ELF]	619 Ohm [CR1206- FX-6190ELF]	62 kOhm [CR0805- JW-623ELF]
604 Ohm [CR0805- FX-6040ELF]	61.9 Ohm [CR1206- FX-61R9ELF]	619 Ohm [CRT0402-FZ- 6190GLF]	62 kOhm [CR1206- FX-6202ELF]

Multisim 14.1 Base Edition Components

62 kOhm [CR1206-JW-623ELF]	62 Ohm [4310M-102-620LF]	62 Ohm [CR0805-FX-62R0GLF]	62 pF [C0805C620KBGAC TU]
62 kOhm [CR2512-JW-623ELF]	62 Ohm [4605X-101-620LF]	62 Ohm [CR0805-JW-620ELF]	62 pF [C1206C620KBGAC TU]
62 kOhm [CRT0603-FY-6202ELF]	62 Ohm [4816P-1-620]	62 Ohm [CR1206-FX-62R0ELF]	62 pF [C1206C620KDGAC TU]
62 kOhm [CRT0805-BW-6202ELF]	62 Ohm [4816P-1-620LF]	62 Ohm [CR1206-JW-620ELF]	62 pF [C1210C620KBGAC TU]
62 kOhm [CRT0805-CX-6202ELF]	62 Ohm [CAT10-620J4LF]	62 Ohm [CR2010-FX-62R0ELF]	62 pF [C1812C620KBGAC TU]
62 mF [C0805C629KBGAC TU]	62 Ohm [CAY10-620J2LF]	62 Ohm [CR2512-FX-62R0ELF]	62 pF [C1825C620KBGAC TU]
62 mOhm [CRL1206-JW-R062ELF]	62 Ohm [CAY10-620J4LF]	62 Ohm [CRM0805-JW-620ELF]	62 pF [C2220C620KBGAC TU]
62 mOhm [CRM2512-FX-R062ELF]	62 Ohm [CAY17-620JALF]	62 Ohm [CRT0805-BW-62R0ELF]	62 pF [C2225C620KBGAC TU]
62 Ohm [4116R-1-620]	62 Ohm [CR0402-FX-62R0GLF]	62 pF [C0402C620K3GACT U]	620 kOhm [CAY16-624J4LF]
62 Ohm [4116R-1-620LF]	62 Ohm [CR0402-JW-620GLF]	62 pF [C0402C620K5GACT U]	620 kOhm [CR0402-FX-6203GLF]
62 Ohm [4116R-2-620]	62 Ohm [CR0603-FX-62R0ELF]	62 pF [C0603C620K5GACT U]	620 kOhm [CR0603-FX-6203ELF]
62 Ohm [4308R-102-620]	62 Ohm [CR0603-JW-620ELF]		
62 Ohm [4310M-102-620]	62 Ohm [CR0805-FX-62R0ELF]		

Multisim 14.1 Base Edition Components

620 kOhm [CR0603-JW-624ELF]	620 mOhm [CRL1206-JW-R620ELF]	620 Ohm [CAY16-621J4LF]	620 pF [C0402C621K5HACTU]
620 kOhm [CR0805-FX-6203ELF]	620 mOhm [CRL2010-FW-R620ELF]	620 Ohm [CR0402-FX-6200GLF]	620 pF [C0603C621K1HACTU]
620 kOhm [CR0805-JW-624ELF]	620 mOhm [CRL2010-JW-R620ELF]	620 Ohm [CR0402-JW-621GLF]	620 pF [C0603C621K3HACTU]
620 kOhm [CR1206-FX-6203ELF]	620 mOhm [CRL2512-JW-R620ELF]	620 Ohm [CR0603-JW-621ELF]	620 pF [C0603C621K5GACTU]
620 kOhm [CR1206-JW-624ELF]	620 Ohm [4114R-2-621]	620 Ohm [CR0805-FX-6200ELF]	620 pF [C0603C621K5HACTU]
620 kOhm [CR2010-JW-624ELF]	620 Ohm [4605X-101-621LF]	620 Ohm [CR0805-JW-621ELF]	620 pF [C0805C621K5GACTU]
620 mOhm [CRL0603-FW-R620ELF]	620 Ohm [4606X-101-621LF]	620 Ohm [CR1206-FX-6200ELF]	620 pF [C1210C621KBGAC TU]
620 mOhm [CRL0603-JW-R620ELF]	620 Ohm [4609X-101-621LF]	620 Ohm [CR1206-JW-621ELF]	620 pF [C1812C621KBGAC TU]
620 mOhm [CRL0805-FW-R620ELF]	620 Ohm [4816P-1-621]	620 Ohm [CR2512-JW-621ELF]	620 pF [C1825C621KBGAC TU]
620 mOhm [CRL0805-JW-R620ELF]	620 Ohm [4816P-1-621LF]	620 Ohm [PWR3014W6200JE]	620 pF [C2220C621KBGAC TU]
620 mOhm [CRL1206-FW-R620ELF]	620 Ohm [4816P-T01-621]	620 pF [C0402C621K1HACTU]	620 pF [C2225C621KBGAC TU]
	620 Ohm [4816P-T01-621LF]	620 pF [C0402C621K3HACTU]	
	620 Ohm [4816P-T02-621]		

Multisim 14.1 Base Edition Components

63.4 kOhm [CR0402-FX- 6342GLF]	634 kOhm [CR1206-FX- 6343ELF]	64.9 Ohm [CR0603- FX-64R9ELF]	649 Ohm [CR0805- FX-6490ELF]
63.4 kOhm [CR0603-FX- 6342ELF]	634 Ohm [CR0402- FX-6340GLF]	64.9 Ohm [CR0805- FX-64R9ELF]	649 Ohm [CR1206- FX-6490ELF]
63.4 kOhm [CR0805-FX- 6342ELF]	634 Ohm [CR0603- FX-6340ELF]	64.9 Ohm [CR1206- FX-64R9ELF]	649 Ohm [CRT0402-FZ- 6490GLF]
63.4 kOhm [CR1206-FX- 6342ELF]	634 Ohm [CR1206- FX-6340ELF]	64.9 Ohm [CRT0805-FY- 64R9ELF]	649 Ohm [CRT0603-PV- 6490ELF]
63.4 kOhm [CRT0603-PW- 6342ELF]	64.9 kOhm [CR0201-FW- 6492GLF]	640455-5	649 Ohm [CRT0805-DZ- 6490ELF]
63.4 Ohm [CR0402- FX-63R4GLF]	64.9 kOhm [CR0402-FX- 6492GLF]	640455-8	65 mOhm [CRA2512-JZ- R065ELF]
63.4 Ohm [CR0603- FX-63R4ELF]	64.9 kOhm [CR0603-FX- 6492ELF]	649 kOhm [CR0603-FX- 6493ELF]	66.5 kOhm [CR0402-FX- 6652GLF]
63.4 Ohm [CR0805- FX-63R4ELF]	64.9 kOhm [CR0805-FX- 6492ELF]	649 kOhm [CR0805-FX- 6493ELF]	66.5 kOhm [CR0603-FX- 6652ELF]
63.4 Ohm [CR1206- FX-63R4ELF]	64.9 kOhm [CR0805-FX- 6492ELF]	649 kOhm [CR1206-FX- 6493ELF]	66.5 kOhm [CR0805-FX- 6652ELF]
634 kOhm [CR0402-FX- 6343GLF]	64.9 kOhm [CR1206-FX- 6492ELF]	649 kOhm [CR2010-FX- 6493ELF]	66.5 kOhm [CR1206-FX- 6652ELF]
634 kOhm [CR0603-FX- 6343ELF]	64.9 kOhm [CRT0603-DZ- 6492ELF]	649 Ohm [CAT16- 6490F8LF]	66.5 Ohm [CR0603- FX-66R5ELF]
634 kOhm [CR0805-FX- 6343ELF]	64.9 kOhm [CRT0603-PW- 6492ELF]	649 Ohm [CR0402- FX-6490GLF]	66.5 Ohm [CR0805- FX-66R5ELF]
		649 Ohm [CR0603- FX-6490ELF]	

Multisim 14.1 Base Edition Components

66.5 Ohm [CR1206-FX-66R5ELF]	665 Ohm [CRT1206-BY-6650ELF]	68 kOhm [4308R-101-683]	68 kOhm [4420P-T02-683]
66.5 Ohm [CR2010-FX-66R5ELF]	670 nH [SRP1235-R67M]	68 kOhm [4308R-101-683LF]	68 kOhm [4604X-102-683LF]
66.5 Ohm [CRT0402-BY-66R5GLF]	68 kOhm [4114R-1-683]	68 kOhm [4308R-102-683]	68 kOhm [4605X-101-683LF]
662 kOhm [CR0402-FX-6623GLF]	68 kOhm [4114R-1-683LF]	68 kOhm [4308R-102-683LF]	68 kOhm [4606X-101-683LF]
665 kOhm [CR0402-FX-6653GLF]	68 kOhm [4114R-2-683]	68 kOhm [4310H-101-683]	68 kOhm [4606X-102-683LF]
665 kOhm [CR0402-FX-6653GLF]	68 kOhm [4114R-2-683LF]	68 kOhm [4310H-101-683LF]	68 kOhm [4607X-101-683LF]
665 kOhm [CR0603-FX-6653ELF]	68 kOhm [4116R-1-683]	68 kOhm [4310R-101-683]	68 kOhm [4608X-101-683LF]
665 kOhm [CR0805-FX-6653ELF]	68 kOhm [4116R-1-683LF]	68 kOhm [4310R-101-683LF]	68 kOhm [4608X-102-683LF]
665 kOhm [CR0805-FX-6653ELF]	68 kOhm [4116R-2-683]	68 kOhm [4310R-102-683]	68 kOhm [4609H-101-683LF]
665 kOhm [CR1206-FX-6653ELF]	68 kOhm [4116R-2-683LF]	68 kOhm [4310R-102-683LF]	68 kOhm [4609X-101-683LF]
665 Ohm [CR0402-FX-6650GLF]	68 kOhm [4306R-101-683]	68 kOhm [4416P-2-683]	68 kOhm [4610H-101-683LF]
665 Ohm [CR0603-FX-6650ELF]	68 kOhm [4306R-101-683LF]	68 kOhm [4416P-T02-683]	68 kOhm [4610H-102-683LF]
665 Ohm [CR0805-FX-6650ELF]	68 kOhm [4306R-102-683]	68 kOhm [4420P-1-683]	68 kOhm [4610X-101-683LF]
665 Ohm [CR1206-FX-6650ELF]	68 kOhm [4306R-102-683LF]	68 kOhm [4420P-2-683]	68 kOhm [4610X-102-683LF]
665 Ohm [CRT0805-BY-6650ELF]	68 kOhm [4308H-102-683LF]	68 kOhm [4420P-T01-683]	68 kOhm [4814P-1-683]

Multisim 14.1 Base Edition Components

68 kOhm [4814P-1-683LF]	68 kOhm [CAT16-6802F4LF]	68 kOhm [CR0805-JW-683ELF]	68 nF [06125C683KAT2W]
68 kOhm [4814P-T01-683]	68 kOhm [CAT16-683J4LF]	68 kOhm [CR0805-JW-683GLF]	68 nF [C0402C683K4RACTU]
68 kOhm [4814P-T01-683LF]	68 kOhm [CAT25-683JALF]	68 kOhm [CR1206-FX-6802ELF]	68 nF [C0402C683K8PACTU]
68 kOhm [4814P-T02-683]	68 kOhm [CAY10-683J4LF]	68 kOhm [CR1206-JW-683ELF]	68 nF [C0402C683K8RACTU]
68 kOhm [4814P-T02-683LF]	68 kOhm [CAY16-6802F4LF]	68 kOhm [CR2010-JW-683ELF]	68 nF [C0402C683K8PACTU]
68 kOhm [4816P-1-683]	68 kOhm [CAY16-683J4LF]	68 kOhm [CR2512-JW-683ELF]	68 nF [C0402C683K9PACTU]
68 kOhm [4816P-1-683LF]	68 kOhm [CAY16-683J8LF]	68 kOhm [CRM2512-JW-683ELF]	68 nF [C0402C683K9RACTU]
68 kOhm [4816P-2-683]	68 kOhm [CAY17-683JALF]	68 mF [C0402C689K8GACTU]	68 nF [C0603C683K3RACTU]
68 kOhm [4816P-2-683LF]	68 kOhm [CR0201-FW-6802GLF]	68 mF [C0805C689KBGAC TU]	68 nF [C0603C683K4RACTU]
68 kOhm [4816P-T01-683]	68 kOhm [CR0402-FX-6802GLF]	68 mF [C1206C689K2GACTU]	68 nF [C0603C683K5RACTU]
68 kOhm [4816P-T01-683LF]	68 kOhm [CR0402-JW-683GLF]	68 nF [0306YC683KAT2A]	68 nF [C0603C683K8RACTU]
68 kOhm [4816P-T02-683]	68 kOhm [CR0603-FX-6802ELF]	68 nF [0306ZC683KAT2A]	68 nF [C0603C683K9RACTU]
68 kOhm [4816P-T02-683LF]	68 kOhm [CR0603-JW-683ELF]	68 nF [05083C683KAT2A]	
68 kOhm [4818P-T01-683]	68 kOhm [CR0805-FX-6802ELF]	68 nF [0508ZC683KAT2S]	
68 kOhm [CAT10-683J4LF]	68 kOhm [CR0805-FX-6802GLF]		

Multisim 14.1 Base Edition Components

68 nF [C0603C683M3VAC TU]	68 nF [C1206C683K2RACT U]	68 nF [C1210C683K1GACT U]	68 nF [C1812C683K1GACT U]
68 nF [C0805C683K1RACT U]	68 nF [C1206C683K3GACT U]	68 nF [C1210C683K1HACT U]	68 nF [C1812C683K1HACT U]
68 nF [C0805C683K3RACT U]	68 nF [C1206C683K3HACT U]	68 nF [C1210C683K1RACT U]	68 nF [C1812C683K1RACT U]
68 nF [C0805C683K4RACT U]	68 nF [C1206C683K5HACT U]	68 nF [C1210C683K2RACT U]	68 nF [C1812C683K2RACT U]
68 nF [C0805C683K5RACT U]	68 nF [C1206C683K5RACT U]	68 nF [C1210C683K3GACT U]	68 nF [C1812C683K5GACT U]
68 nF [C0805C683K8RACT U]	68 nF [C1206C683KARACT U]	68 nF [C1210C683K3HACT U]	68 nF [C1812C683K5HACT U]
68 nF [C0805C683M5UAC TU]	68 nF [C1206C683M5UAC TU]	68 nF [C1210C683K5GACT U]	68 nF [C1812C683K5RACT U]
68 nF [C0805F683K3RACT U]	68 nF [C1206F683K1RACT U]	68 nF [C1210C683K5HACT U]	68 nF [C2220C683K1GACT U]
68 nF [C0805F683K4RACT U]	68 nF [C1206F683K3RACT U]	68 nF [C1210C683K5RACT U]	68 nF [C2220C683K2GACT U]
68 nF [C0805F683K5RACT U]	68 nF [C1206F683K4RACT U]	68 nF [C1210C683KARACT U]	68 nF [C2220C683K5GACT U]
68 nF [C1206C683K1RACT U]	68 nF [C1206F683K5RACT U]	68 nF [C1210F683K2RACT U]	68 nF [CA064C683K4RACT U]

Multisim 14.1 Base Edition Components

68 nF [CDR05BX683BKSM]	68 nF [MDC15683K100B5 3P3TUBE]	68 nF [MDS10683K400A5 2P3TUBE]	68 nF [SPC16.5683K400C 31TR24]
68 nF [GMC5.7683K50J31 TR12]	68 nF [MDC15683K250B5 3P3TUBE]	68 nF [MDS10683K50A52 P3TUBE]	68 nF [SPC16.5683K630C 31TR24]
68 nF [GMC7.3682K250K3 1TR12]	68 nF [MDC15683K400B5 3P3TUBE]	68 nF [MDS15683K100B5 3P3TUBE]	68 nF [W2L1YC683MAT1A]
68 nF [GMC7.3683K63K31 TR12]	68 nF [MDC15683K50B53 P3TUBE]	68 nF [MDS15683K250B5 3P3TUBE]	68 nF [W2L1YC683MAT1S]
68 nF [GPC7.3683K63K35 TR12]	68 nF [MDC15683K630B5 3P3TUBE]	68 nF [MDS15683K400B5 3P3TUBE]	68 Ohm [4114R-1- 680]
68 nF [MDC10683K100A5 2P3TUBE]	68 nF [MDK10683K100A5 2P3TUBE]	68 nF [MDS15683K630B5 3P3TUBE]	68 Ohm [4114R-1- 680LF]
68 nF [MDC10683K250A5 2P3TUBE]	68 nF [MDK10683K250A5 2P3TUBE]	68 nF [MMC5.7683K50J3 1TR12]	68 Ohm [4114R-2- 680]
68 nF [MDC10683K400A5 2P3TUBE]	68 nF [MDK10683K400A5 2P3TUBE]	68 nF [MMC7.3683K100K 31TR12]	68 Ohm [4114R-2- 680LF]
68 nF [MDC10683K50A52 P3TUBE]	68 nF [MDK10683K50A52 P3TUBE]	68 nF [MMC7.3683K50K3 1TR12]	68 Ohm [4116R-1- 680]
68 nF [MDC10683K630A5 4P3TUBE]	68 nF [MDS10683K100A5 2P3TUBE]	68 nF [SPC10.2683K100A 31TR16]	68 Ohm [4116R-1- 680LF]
68 nF [MDC10683K630A5 4P4TUBE]	68 nF [MDS10683K250A5 2P3TUBE]	68 nF [SPC12.7683K250B 31TR24]	68 Ohm [4116R-2- 680LF]
			68 Ohm [4306M- 101-680]
			68 Ohm [4306M- 101-680LF]

Multisim 14.1 Base Edition Components

68 Ohm [4306R-101-680]	68 Ohm [4310M-102-680]	68 Ohm [4606X-101-680LF]	68 Ohm [4814P-T02-680]
68 Ohm [4306R-101-680LF]	68 Ohm [4310M-102-680LF]	68 Ohm [4606X-102-680LF]	68 Ohm [4816P-1-680]
68 Ohm [4306R-102-680]	68 Ohm [4310R-101-680]	68 Ohm [4607X-101-680LF]	68 Ohm [4816P-1-680LF]
68 Ohm [4306R-102-680LF]	68 Ohm [4310R-101-680LF]	68 Ohm [4608H-102-680LF]	68 Ohm [4816P-2-680]
68 Ohm [4308H-102-680]	68 Ohm [4310R-102-680]	68 Ohm [4608X-101-680LF]	68 Ohm [4816P-2-680LF]
68 Ohm [4308H-102-680LF]	68 Ohm [4310R-102-680LF]	68 Ohm [4608X-102-680LF]	68 Ohm [4816P-T01-680]
68 Ohm [4308M-101-680]	68 Ohm [4416P-1-680]	68 Ohm [4608X-AP2-680LF]	68 Ohm [4816P-T01-680LF]
68 Ohm [4308M-101-680LF]	68 Ohm [4416P-2-680]	68 Ohm [4609X-101-680LF]	68 Ohm [4816P-T02-680]
68 Ohm [4308M-102-680]	68 Ohm [4420P-1-680]	68 Ohm [4610X-101-680LF]	68 Ohm [4816P-T02-680LF]
68 Ohm [4308R-101-680]	68 Ohm [4420P-2-680]	68 Ohm [4610X-102-680LF]	68 Ohm [CAT10-680J4LF]
68 Ohm [4308R-101-680LF]	68 Ohm [4420P-T01-680]	68 Ohm [4612X-102-680LF]	68 Ohm [CAT16-680J4LF]
68 Ohm [4308R-102-680]	68 Ohm [4420P-T02-680]	68 Ohm [4614X-102-680LF]	68 Ohm [CAT16-680J8LF]
68 Ohm [4308R-102-680LF]	68 Ohm [4604X-101-680LF]	68 Ohm [4814P-1-680]	68 Ohm [CAT16-68R0F4LF]
68 Ohm [4309R-101-680]	68 Ohm [4604X-102-680LF]	68 Ohm [4814P-T01-680]	68 Ohm [CAT25-680JALF]
68 Ohm [4310M-101-680]	68 Ohm [4605X-101-680LF]	68 Ohm [4814P-T01-680LF]	68 Ohm [CAY10-680J4LF]

Multisim 14.1 Base Edition Components

68 Ohm [CAY16-680J4GLF]	68 Ohm [CR2010-JW-680ELF]	68 Ohm [PWR6327N68R0FE]	68 pF [C0805C680K1GACT U]
68 Ohm [CAY16-680J4LF]	68 Ohm [CR2512-JW-680ELF]	68 Ohm [PWR6327W68R0J]	68 pF [C0805C680K2GACT U]
68 Ohm [CAY16-680J8LF]	68 Ohm [CRM1206-FX-68R0ELF]	68 Ohm [PWR6327W68R0JE]	68 pF [C0805C680K5GACT U]
68 Ohm [CAY16-68R0F4LF]	68 Ohm [CRM2512-JW-680ELF]	68 Ohm [WS2M68R0J]	68 pF [C0805C680KBGAC TU]
68 Ohm [CAY17-680JALF]	68 Ohm [FW10A68R0JA]	68 pF [C0201C680K3GACT U]	68 pF [C1206C680K1GACT U]
68 Ohm [CR0402-FX-68R0GLF]	68 Ohm [FW20A68R0JA]	68 pF [C0402C680K3GACT U]	68 pF [C1206C680K2GACT U]
68 Ohm [CR0402-JW-680GLF]	68 Ohm [FW30A68R0JA]	68 pF [C0402C680K5GACT U]	68 pF [C1206C680K5GACT U]
68 Ohm [CR0603-FX-68R0ELF]	68 Ohm [FW50A68R0JA]	68 pF [C0402C680K8GACT U]	68 pF [C1206C680KBGAC TU]
68 Ohm [CR0603-JW-680ELF]	68 Ohm [FW70A68R0JA]	68 pF [C0603C680K2GACT U]	68 pF [C1206C680KDGAC TU]
68 Ohm [CR0805-FX-68R0ELF]	68 Ohm [PWR2615W68R0J]	68 pF [C0603C680K3GACT U]	68 pF [C1206C680KGGAC TU]
68 Ohm [CR0805-JW-680ELF]	68 Ohm [PWR2615W68R0JE]	68 pF [C0603C680K4GACT U]	68 pF [C1210C680KBGAC TU]
68 Ohm [CR1206-FX-68R0ELF]	68 Ohm [PWR4525W68R0J]	68 pF [C0603C680K5GACT U]	
68 Ohm [CR1206-JW-680ELF]	68 Ohm [PWR4525W68R0JE]		
68 Ohm [CR1206-JW-680GLF]			

Multisim 14.1 Base Edition Components

68 pF [C1812C680KBGAC TU]	68 uF [4TPH68MHA]	68 uF [EEFCX1C680R]	68 uF [T491B686M010AT]
68 pF [C1825C680KBGAC TU]	68 uF [4TPU68MSI]	68 uF [EEFHX1A680R]	68 uF [T491C686M004AT]
68 pF [C2220C680KBGAC TU]	68 uF [6TPB68M]	68 uF [EEFHX1C680R]	68 uF [T491C686M006AT]
68 pF [C2220C680KBGAC TU]	68 uF [A700D686M008AT E015]	68 uF [EEFLR0J680R]	68 uF [T491C686M010AT]
68 pF [C2225C680KBGAC TU]	68 uF [A700D686M008AT E018]	68 uF [EEFSR0J680R]	68 uF [T491C686M016AT]
68 pF [CA064C680K5GAC TU]	68 uF [A700D686M010AT E015]	68 uF [EEHZA1H680P]	68 uF [T491D686M004AT]
68 pF [CA064C680K8GAC TU]	68 uF [A700D686M010AT E018]	68 uF [EEHZA1V680XP]	68 uF [T491D686M006AT]
68 pF [CDR01BP680BKSM]	68 uF [A700V686M006AT E018]	68 uF [EEHZC1V680XP]	68 uF [T491D686M010AT]
68 uF [10SVPC68MV]	68 uF [A700V686M006AT E025]	68 uF [LDEDD3680KA5N0 0]	68 uF [T491D686M016AT]
68 uF [10TPC68M]	68 uF [A700V686M006AT E028]	68 uF [T419G686M010AH 4250]	68 uF [T491D686M020AT]
68 uF [16SVPC68M]	68 uF [EEFCS0J680R]	68 uF [T491A686M004AT]	68 uF [T491D686M025AT]
68 uF [16TQC68MYF]	68 uF [EEFCT1A680R]	68 uF [T491A686M006AT]	68 uF [T491U686M004AT]
68 uF [20SVP68M]	68 uF [EEFCX1A680R]	68 uF [T491B686M004AT]	
68 uF [4TPB68M]		68 uF [T491B686M006AT]	

Multisim 14.1 Base Edition Components

68 uF [T491U686M006AT]	68 uF [T494D686M004AT]	68 uF [T494X686M025AT]	68 uF [T495D686M020AT E150]
68 uF [T491U686M010AT]	68 uF [T494D686M006AT]	68 uF [T495B686M010AT E900]	68 uF [T495D686M025AT E150]
68 uF [T491V686M010AT]	68 uF [T494D686M010AT]	68 uF [T495C686M010AT E225]	68 uF [T495D686M025AT E200]
68 uF [T491V686M016AT]	68 uF [T494D686M016AT]	68 uF [T495D686M006AT E175]	68 uF [T495V686M010AT E100]
68 uF [T491X686M020AT]	68 uF [T494D686M020AT]	68 uF [T495D686M010AT E070]	68 uF [T495V686M010AT E140]
68 uF [T491X686M025AT]	68 uF [T494D686M025AT]	68 uF [T495D686M010AT E090]	68 uF [T495V686M016AT E300]
68 uF [T494A686M004AT]	68 uF [T494U686M004AT]	68 uF [T495D686M010AT E150]	68 uF [T495X686M010AT E150]
68 uF [T494A686M006AT]	68 uF [T494U686M006AT]	68 uF [T495D686M016AT E070]	68 uF [T495X686M020AT E150]
68 uF [T494B686M004AT]	68 uF [T494U686M010AT]	68 uF [T495D686M016AT E100]	68 uF [T495X686M025AT E125]
68 uF [T494B686M010AT]	68 uF [T494V686M010AT]	68 uF [T495D686M016AT E150]	68 uF [T495X686M025AT E200]
68 uF [T494C686M004AT]	68 uF [T494V686M016AT]	68 uF [T495D686M020AT E070]	68 uF [T513X686M025AH 6110]
68 uF [T494C686M006AT]	68 uF [T494X686M020AT]		
68 uF [T494C686M010AT]			
68 uF [T494C686M016AT]			

Multisim 14.1 Base Edition Components

68 uF [T520A686M006AT E150]	68 uF [T520C686M006AT E100]	68 uF [T520V686M010AT E060]	68 uF [TAJB686K006RNJ]
68 uF [T520A686M2R5AT E070]	68 uF [T520C686M010AT E045]	68 uF [T520V686M010AT E100]	68 uF [TAJB686K010RNJ]
68 uF [T520A686M2R5AT E080]	68 uF [T520T686M004AT E070]	68 uF [T520W686M010AT E040]	68 uF [TAJC686K006RNJ]
68 uF [T520B686M004AT E025]	68 uF [T520T686M006AT E070]	68 uF [T521D686M016AT E050]	68 uF [TAJC686K016RNJ]
68 uF [T520B686M004AT E035]	68 uF [T520T686M006AT E150]	68 uF [T521V686M016AT E050]	68 uF [TAJD686K006RNJ]
68 uF [T520B686M004AT E040]	68 uF [T520U686M004AT E055]	68 uF [T521V686M016AT E090]	68 uF [TAJD686K016RNJ]
68 uF [T520B686M004AT E070]	68 uF [T520U686M006AT E055]	68 uF [T525B686M004AT E080]	68 uF [TAJD686K020RNJ]
68 uF [T520B686M006AT E025]	68 uF [T520U686M006AT E070]	68 uF [T525B686M006AT E080]	68 uF [TAJE686K020RNJ]
68 uF [T520B686M006AT E035]	68 uF [T520V686M010AT E025]	68 uF [T525T686M004AT E080]	68 uF [TAJT686K004RNJ]
68 uF [T520B686M006AT E040]	68 uF [T520V686M010AT E040]	68 uF [T543U686M006AT E055]	68 uF [TAJV686K025RNJ]
68 uF [T520B686M006AT E070]	68 uF [T520V686M010AT E045]	68 uF [TAJA686K002RNJ]	68 uF [TAJW686K006RNJ]
		68 uF [TAJB686K004RNJ]	

Multisim 14.1 Base Edition Components

68 uF [TAJX686K016RNJ]	68 uF [TPSC686K010R020 0]	68 uF [TPSD686K020R030 0]	68 uF [TPSW686K006R02 50]
68 uF [TAJY686K010RNJ]	68 uF [TPSC686K010R030 0]	68 uF [TPSE686K020R012 5]	68 uF [TPSW686K010R01 00]
68 uF [TAJY686K016RNJ]	68 uF [TPSC686K016R020 0]	68 uF [TPSE686K020R015 0]	68 uF [TPSY686K010R010 0]
68 uF [THJC686K006RJN]	68 uF [TPSD686K010R010 0]	68 uF [TPSE686K020R020 0]	68 uF [TPSY686K010R020 0]
68 uF [THJD686K016RJN]	68 uF [TPSD686K010R015 0]	68 uF [TPSE686K025R012 5]	68 uF [TPSY686K016R020 0]
68 uF [TPMD686K016R00 50]	68 uF [TPSD686K016R007 0]	68 uF [TPSE686K025R020 0]	68 uF [TPSY686K016R025 0]
68 uF [TPME686K025R00 45]	68 uF [TPSD686K016R010 0]	68 uF [TPSV686K025R008 0]	68 uF [TRJC686K010RRJ]
68 uF [TPME686K025R00 55]	68 uF [TPSD686K016R015 0]	68 uF [TPSV686K025R009 5]	68 uF [TRJD686K020RRJ]
68 uF [TPSB686K006R035 0]	68 uF [TPSD686K020R007 0]	68 uF [TPSV686K025R015 0]	68 uF [TRJE686K020RRJ]
68 uF [TPSB686K006R050 0]	68 uF [TPSD686K020R015 0]	68 uF [TPSV686K025R020 0]	68 uH [SDE0403A- 680K]
68 uF [TPSC686K006R015 0]	68 uF [TPSD686K020R020 0]	68 uF [TPSW686K006R01 25]	68 uH [SDE0604A- 680K]
68 uF [TPSC686K006R020 0]			68 uH [SDE0805A- 680K]
			68 uH [SDE1006A- 680K]

Multisim 14.1 Base Edition Components

68 uH [SDR0302-680KL]	68 uH [SDR1307A-680K]	68 uH [SRR0735A-680M]	68 uH [SRR1260-680M]
68 uH [SDR0403-680KL]	68 uH [SDR1806-680ML]	68 uH [SRR0745A-680M]	68 uH [SRR1260A-680M]
68 uH [SDR0503-680KL]	68 uH [SDR6603-680M]	68 uH [SRR0804-680K]	68 uH [SRR1280-680M]
68 uH [SDR0603-680KL]	68 uH [SDR7030-680K]	68 uH [SRR0805-680K]	68 uH [SRR1806-680M]
68 uH [SDR0604-680KL]	68 uH [SDR7045-680K]	68 uH [SRR0905-680Y]	68 uH [SRR3011-680YL]
68 uH [SDR0703-680KL]	68 uH [SRN4018-680M]	68 uH [SRR0906-680ML]	68 uH [SRR4011-680YL]
68 uH [SDR0805-680KL]	68 uH [SRN4026-680M]	68 uH [SRR0908-680ML]	68 uH [SRR4018-680Y]
68 uH [SDR0906-680KL]	68 uH [SRN6028-680M]	68 uH [SRR1003-680M]	68 uH [SRR4028-680Y]
68 uH [SDR1005-680KL]	68 uH [SRN6045-680M]	68 uH [SRR1005-680Y]	68 uH [SRR5018-680Y]
68 uH [SDR1006-680KL]	68 uH [SRN8040-680M]	68 uH [SRR1205-680YL]	68 uH [SRR5028-680Y]
68 uH [SDR1030-680M]	68 uH [SRP1770TA-680M]	68 uH [SRR1206-680YL]	68 uH [SRR6028-680Y]
68 uH [SDR1045-680M]	68 uH [SRP7050TA-680M]	68 uH [SRR1208-680YL]	68 uH [SRR6038-680Y]
68 uH [SDR1105-680KL]	68 uH [SRR0603-680KL]	68 uH [SRR1210-680M]	68 uH [SRR6040A-680M]
68 uH [SDR1305-680M]	68 uH [SRR0604-680KL]	68 uH [SRR1210A-680M]	68 uH [SRR6603-680ML]
68 uH [SDR1307-680KL]	68 uH [SRR0618-680ML]	68 uH [SRR1240-680M]	68 uH [SRR7032-680M]

Multisim 14.1 Base Edition Components

68 uH [SRR7045-680M]	68 uH [SRU6011-680Y]	68.1 kOhm [CRT0603-BY-6812ELF]	680 kOhm [4114R-1-684LF]
68 uH [SRU1028-680Y]	68 uH [SRU6018-680Y]	68.1 kOhm [CRT0805-BY-6812ELF]	680 kOhm [4116R-1-684]
68 uH [SRU1028A-680Y]	68 uH [SRU6025-680Y]	68.1 kOhm [CRT0805-CX-6812ELF]	680 kOhm [4116R-1-684LF]
68 uH [SRU1038-680Y]	68 uH [SRU6025A-680Y]	68.1 kOhm [CRT1206-FZ-6812ELF]	680 kOhm [4116R-2-684]
68 uH [SRU1038A-680Y]	68 uH [SRU8028-680Y]	68.1 Ohm [CR0402-FX-68R1GLF]	680 kOhm [4306R-102-684]
68 uH [SRU1048-680Y]	68 uH [SRU8028A-680Y]	68.1 Ohm [CR0603-FX-68R1ELF]	680 kOhm [4306R-102-684LF]
68 uH [SRU1048A-680Y]	68 uH [SRU8043-680Y]	68.1 Ohm [CR0805-FX-68R1ELF]	680 kOhm [4308R-101-684]
68 uH [SRU1063-680Y]	68.1 kOhm [CAY16-6812F4LF]	68.1 Ohm [CR0805-FX-68R1ELF]	680 kOhm [4308R-102-684]
68 uH [SRU2016-680Y]	68.1 kOhm [CR0201-FW-6812GLF]	68.1 Ohm [CR0805-FX-68R1GLF]	680 kOhm [4308R-102-684LF]
68 uH [SRU3028-680Y]	68.1 kOhm [CR0402-FX-6812GLF]	68.1 Ohm [CR1206-FX-68R1ELF]	680 kOhm [4310R-101-684]
68 uH [SRU5011-680Y]	68.1 kOhm [CR0603-FX-6812ELF]	68.1 Ohm [CR2512-FX-68R1ELF]	680 kOhm [4310R-101-684LF]
68 uH [SRU5016-680Y]	68.1 kOhm [CR0805-FX-6812ELF]	68.1 Ohm [CRM1206-FX-68R1ELF]	680 kOhm [4310R-102-684]
68 uH [SRU5018-680Y]	68.1 kOhm [CR1206-FX-6812ELF]	68.1 Ohm [CRT0805-BY-68R1ELF]	680 kOhm [4605X-101-684LF]
68 uH [SRU5028-680Y]	68.1 kOhm [CR1206-FX-6812ELF]	680 kOhm [4114R-1-684]	680 kOhm [4606X-101-684LF]
68 uH [SRU5028A-680Y]			680 kOhm [4606X-102-684LF]

Multisim 14.1 Base Edition Components

680 kOhm [4608X-101-684LF]	680 kOhm [CAT16-684J8LF]	680 kOhm [CR1206-JW-684ELF]	680 mOhm [CRL2512-FW-R680ELF]
680 kOhm [4608X-102-684LF]	680 kOhm [CAT25-684JALF]	680 kOhm [CR1206-JW-684GLF]	680 mOhm [CRL2512-JW-R680ELF]
680 kOhm [4609X-101-684LF]	680 kOhm [CAY10-684J4LF]	680 kOhm [CRM1206-FX-6803ELF]	680 mOhm [CRM1206-FX-R680ELF]
680 kOhm [4610X-101-684LF]	680 kOhm [CAY16-6803F4LF]	680 mOhm [CRL0603-FW-R680ELF]	680 mOhm [CRM2512-FX-R680ELF]
680 kOhm [4610X-102-684LF]	680 kOhm [CAY16-684J4LF]	680 mOhm [CRL0603-JW-R680ELF]	680 mOhm [PWR1913WR680J]
680 kOhm [4814P-T01-684]	680 kOhm [CAY16-684J8LF]	680 mOhm [CRL0805-FW-R680ELF]	680 mOhm [PWR1913WR680JE]
680 kOhm [4816P-2-684]	680 kOhm [CR0402-FX-6803GLF]	680 mOhm [CRL0805-JW-R680ELF]	680 mOhm [PWR2615WR680J]
680 kOhm [4816P-T01-684]	680 kOhm [CR0402-JW-684GLF]	680 mOhm [CRL1206-FW-R680ELF]	680 mOhm [PWR2615WR680JE]
680 kOhm [4816P-T01-684LF]	680 kOhm [CR0603-FX-6803ELF]	680 mOhm [CRL1206-JW-R680ELF]	680 mOhm [PWR263S-20-R680F]
680 kOhm [4816P-T02-684]	680 kOhm [CR0603-JW-684ELF]	680 mOhm [CRL2010-FW-R680ELF]	680 mOhm [PWR3014WR680F E]
680 kOhm [4820P-2-684]	680 kOhm [CR0805-FX-6803ELF]	680 mOhm [CRL2010-JW-R680ELF]	680 mOhm [PWR4525WR680J]
680 kOhm [4820P-T02-684]	680 kOhm [CR0805-JW-684ELF]		
680 kOhm [4820P-T02-684LF]	680 kOhm [CR1206-FX-6803ELF]		

Multisim 14.1 Base Edition Components

680 mOhm [PWR4525WR680JE]	680 nF [C0805C684M4VAC TU]	680 nF [C1210C684M3VAC TU]	680 nF [C1825C684K5RACT U]
680 mOhm [PWR6327WR680J]	680 nF [C1206C684K3RACT U]	680 nF [C1210C684M5VAC TU]	680 nF [C1825C684KARACT U]
680 mOhm [PWR6327WR680JE]	680 nF [C1206C684K4RACT U]	680 nF [C1210F684K3RACT U]	680 nF [C2220C684K1RACT U]
680 nF [05086C684KAT2A]	680 nF [C1206C684K5RACT U]	680 nF [C1210F684K4RACT U]	680 nF [C2220C684K5RACT U]
680 nF [0508ZC684KAT2A]	680 nF [C1206C684K8RACT U]	680 nF [C1210F684K5RACT U]	680 nF [C2220C684KARACT U]
680 nF [0612YC684KAT2W]	680 nF [C1206C684M3VAC TU]	680 nF [C1812C684K5RACT U]	680 nF [C2225C684K1RACT U]
680 nF [0612ZC684KAT2V]	680 nF [C1206C684M4VAC TU]	680 nF [C1812C684M5UAC TU]	680 nF [C2225C684K5RACT U]
680 nF [C0603C684K4PACT U]	680 nF [C1206F684K4RACT U]	680 nF [C1812F684K1RACT U]	680 nF [C2225C684KARACT U]
680 nF [C0603C684K8PACT U]	680 nF [C1210C684K3RACT U]	680 nF [C1812F684K3RACT U]	680 nF [MDC10684K100A5 2P3TUBE]
680 nF [C0805C684K3PACT U]	680 nF [C1210C684K4RACT U]	680 nF [C1812F684K5RACT U]	680 nF [MDC10684K250A5 5P3TUBE]
680 nF [C0805C684K4RACT U]	680 nF [C1210C684K5RACT U]	680 nF [C1825C684K1RACT U]	680 nF [MDC10684K250A5 5P4TUBE]
680 nF [C0805C684K8RACT U]			

Multisim 14.1 Base Edition Components

680 nF [MDC10684K250A5 5P3TUBE]	680 nF [MDS15684K50B53 P3TUBE]	680 nF [T496C684M050AT 6110]	680 nF [THJB684K035RJN]
680 nF [MDC10684K50A52 P3TUBE]	680 nF [SPC16.5684K100C 31TR24]	680 nF [TAJA684K025RNJ]	680 nF [TPSA684K025R600 0]
680 nF [MDC15684K100B5 3P3TUBE]	680 nF [T491A684M020AT]	680 nF [TAJA684K035RNJ]	680 nF [TPSA684K035R600 0]
680 nF [MDC15684K250B5 3P3TUBE]	680 nF [T491A684M025AT]	680 nF [TAJB684K035RNJ]	680 nF [TPSB684K050R400 0]
680 nF [MDC15684K50B53 P3TUBE]	680 nF [T491A684M035AT]	680 nF [TAJC684K050RNJ]	680 nF [TRJA684K025RRJ]
680 nF [MDK10684K50A52 P3TUBE]	680 nF [T491B684M035AT]	680 nF [TAJR684K016RNJ]	680 nF [W2L1ZC684MAT1A]
680 nF [MDK10684K50A52 P3TUBE]	680 nF [T491B684M050AT]	680 nF [TAJR684K020RNJ]	680 nF [W3L16C684MAT1S]
680 nF [MDK15684K250B5 3P3TUBE]	680 nF [T491C684M050AT]	680 nF [TAJR684K025RNJ]	680 nF [W3L16C684MAT1S]
680 nF [MDS10684K100A5 2P3TUBE]	680 nF [T494A684M020AT]	680 nF [TAJS684K016RNJ]	680 nH [SDR1005- R68ML]
680 nF [MDS10684K50A52 P3TUBE]	680 nF [T494A684M025AT]	680 nF [TAJS684K020RNJ]	680 nH [SRN2010- R68M]
680 nF [MDS10684K50A52 P3TUBE]	680 nF [T494A684M035AT]	680 nF [TAJS684K025RNJ]	680 nH [SRN2510- R68M]
680 nF [MDS15684K100B5 3P3TUBE]	680 nF [T494A684M035AT]	680 nF [TAJS684K035RNJ]	680 nH [SRN2512- R68M]
680 nF [MDS15684K250B5 3P3TUBE]	680 nF [T494B684M035AT]	680 nF [TAJT684K020RNJ]	680 nH [SRP1040- R68M]
680 nF [MDS15684K250B5 3P3TUBE]	680 nF [T494B684M050AT]	680 nF [TAJT684K035RNJ]	680 nH [SRP1235- R68M]
		680 nF [THJA684K025RJN]	

Multisim 14.1 Base Edition Components

680 nH [SRP1250-R68M]	680 Ohm [4114R-2-681LF]	680 Ohm [4308M-101-681]	680 Ohm [4310R-102-681]
680 nH [SRP1265A-R68M]	680 Ohm [4116R-1-681]	680 Ohm [4308M-101-681LF]	680 Ohm [4310R-102-681LF]
680 nH [SRP1270-R68M]	680 Ohm [4116R-1-681LF]	680 Ohm [4308R-101-681]	680 Ohm [4416P-1-681]
680 nH [SRP4020-R68M]	680 Ohm [4116R-2-681]	680 Ohm [4308R-101-681LF]	680 Ohm [4416P-2-681]
680 nH [SRP4020TA-R68M]	680 Ohm [4116R-2-681LF]	680 Ohm [4308R-102-681]	680 Ohm [4416P-2-681LF]
680 nH [SRP5015TA-R68M]	680 Ohm [4304M-102-681]	680 Ohm [4308R-102-681LF]	680 Ohm [4416P-T01-681]
680 nH [SRP5030TA-R68M]	680 Ohm [4304M-102-681LF]	680 Ohm [4309R-101-681]	680 Ohm [4416P-T02-681]
680 nH [SRP5030T-R68M]	680 Ohm [4306H-102-681]	680 Ohm [4309R-101-681LF]	680 Ohm [4420P-2-681]
680 nH [SRP6540-R68M]	680 Ohm [4306H-102-681LF]	680 Ohm [4310H-101-681]	680 Ohm [4420P-T01-681]
680 nH [SRP7028A-R68M]	680 Ohm [4306R-101-681]	680 Ohm [4310H-101-681LF]	680 Ohm [4420P-T02-681]
680 nH [SRP7030-R68FM]	680 Ohm [4306R-101-681LF]	680 Ohm [4310M-101-681]	680 Ohm [4604X-101-681LF]
680 nH [SRP7050TA-R68M]	680 Ohm [4306R-102-681]	680 Ohm [4310M-101-681LF]	680 Ohm [4604X-102-681LF]
680 Ohm [4114R-1-681]	680 Ohm [4306R-102-681LF]	680 Ohm [4310M-102-681]	680 Ohm [4605X-101-681LF]
680 Ohm [4114R-1-681LF]	680 Ohm [4308H-101-681]	680 Ohm [4310R-101-681]	680 Ohm [4606H-102-681LF]
680 Ohm [4114R-2-681]	680 Ohm [4308H-101-681LF]	680 Ohm [4310R-101-681LF]	680 Ohm [4606X-101-681LF]

Multisim 14.1 Base Edition Components

680 Ohm [4606X-102-681LF]	680 Ohm [4814P-2-681]	680 Ohm [CAT10-681J4LF]	680 Ohm [CR0603-JW-681ELF]
680 Ohm [4607X-101-681LF]	680 Ohm [4814P-2-681LF]	680 Ohm [CAT16-6800F4LF]	680 Ohm [CR0805-FX-6800ELF]
680 Ohm [4608H-102-681LF]	680 Ohm [4814P-T01-681]	680 Ohm [CAT16-681J2LF]	680 Ohm [CR0805-FX-6800GLF]
680 Ohm [4608X-101-681LF]	680 Ohm [4814P-T01-681LF]	680 Ohm [CAT16-681J4LF]	680 Ohm [CR0805-JW-681ELF]
680 Ohm [4608X-102-681LF]	680 Ohm [4814P-T02-681]	680 Ohm [CAT16-681J8LF]	680 Ohm [CR1206-FX-6800ELF]
680 Ohm [4608X-AP2-681LF]	680 Ohm [4816P-1-681]	680 Ohm [CAT25-681JALF]	680 Ohm [CR1206-FX-6800GLF]
680 Ohm [4609M-101-681LF]	680 Ohm [4816P-1-681LF]	680 Ohm [CAY10-681J4LF]	680 Ohm [CR1206-JW-681ELF]
680 Ohm [4609X-101-681LF]	680 Ohm [4816P-2-681]	680 Ohm [CAY16-6800F4LF]	680 Ohm [CR1206-JW-681GLF]
680 Ohm [4609X-AP1-681LF]	680 Ohm [4816P-2-681LF]	680 Ohm [CAY16-681J4LF]	680 Ohm [CR2010-JW-681ELF]
680 Ohm [4610H-101-681LF]	680 Ohm [4816P-T01-681]	680 Ohm [CAY16-681J8LF]	680 Ohm [CR2512-JW-681ELF]
680 Ohm [4610X-101-681LF]	680 Ohm [4816P-T01-681LF]	680 Ohm [CAY17-681JALF]	680 Ohm [CRM1206-FX-6800ELF]
680 Ohm [4610X-102-681LF]	680 Ohm [4816P-T02-681]	680 Ohm [CR0201-FW-6800GLF]	680 Ohm [CRM2512-JW-681ELF]
680 Ohm [4610X-AP1-681LF]	680 Ohm [4816P-T02-681LF]	680 Ohm [CR0402-FX-6800GLF]	680 Ohm [CRT0805-DY-6800ELF]
680 Ohm [4611X-101-681LF]	680 Ohm [4820P-1-681]	680 Ohm [CR0402-JW-681GLF]	680 Ohm [PWR163S-25-6800F]
680 Ohm [4612X-102-681LF]	680 Ohm [4820P-T01-681]	680 Ohm [CR0603-FX-6800ELF]	

Multisim 14.1 Base Edition Components

680 Ohm [PWR163S-25-6800JE]	680 pF [C0402C681K5HACT U]	680 pF [C0603C681K5RACT U]	680 pF [C1206C681KCGAC TU]
680 Ohm [PWR2615W6800J]	680 pF [C0402C681K5RACT U]	680 pF [C0805C681K1GACT U]	680 pF [C1210C681KBGAC TU]
680 Ohm [PWR2615W6800JE]	680 pF [C0603C681K1HACT U]	680 pF [C0805C681K1RACT U]	680 pF [C1210C681KCGAC TU]
680 Ohm [PWR4525W6800J]	680 pF [C0603C681K1RACT U]	680 pF [C0805C681K2RACT U]	680 pF [C1210C681KDGAC TU]
680 Ohm [PWR4525W6800JE]	680 pF [C0603C681K2RACT U]	680 pF [C0805C681K4GACT U]	680 pF [C1812C681KBGAC TU]
680 Ohm [PWR6327W6800J]	680 pF [C0603C681K3GACT U]	680 pF [C0805C681K4RACT U]	680 pF [C1825C681KBGAC TU]
680 Ohm [PWR6327W6800JE]	680 pF [C0603C681K3HACT U]	680 pF [C0805C681K5GACT U]	680 pF [C2220C681KBGAC TU]
680 pF [C0402C681K1HACT U]	680 pF [C0603C681K3RACT U]	680 pF [C0805C681K5RACT U]	680 pF [C2220C681KZGACT U]
680 pF [C0402C681K3GACT U]	680 pF [C0603C681K4RACT U]	680 pF [C1206C681K1GACT U]	680 pF [C2225C681KBGAC TU]
680 pF [C0402C681K3HACT U]	680 pF [C0603C681K5GACT U]	680 pF [C1206C681K2GACT U]	680 pF [GPC7.3681K160K3 1TR12]
680 pF [C0402C681K3RACT U]	680 pF [C0603C681K5HACT U]	680 pF [C1206C681K5GACT U]	680 pF [GPC7.3681K63K31 TR12]

Multisim 14.1 Base Edition Components

680 pF [GPC7.3682K630K3 7TR12]	680 uF [T491D687M004AT]	680 uF [T513X687M004AH 6110]	680 uF [T520X687M004AT E010]
680 pF [SPC7.3681K100K31 TR12]	680 uF [T491E687M006AT]	680 uF [T513X687M006AH 6110]	680 uF [T520X687M004AT E015]
680 pF [SPC7.3681K250K31 TR12]	680 uF [T491X687M004AT]	680 uF [T513X687M006AH 6120]	680 uF [T520X687M004AT E035]
680 pF [SPC7.3681K400K31 TR12]	680 uF [T494D687M004AT]	680 uF [T520D687M003AT E015]	680 uF [T520Y687M004AT E010]
680 pF [SPC7.3681K630K31 TR12]	680 uF [T494X687M004AT]	680 uF [T520D687M003AT E040]	680 uF [T520Y687M004AT E015]
680 uF [2R5TPE680MCL]	680 uF [T510E687M006AT E012]	680 uF [T520D687M004AT E012]	680 uF [T520Y687M004AT E025]
680 uF [2R5TPE680MFL]	680 uF [T510E687M006AT E023]	680 uF [T520D687M004AT E015]	680 uF [T520Y687M2R5AT E015]
680 uF [2R5TPF680M6L]	680 uF [T510X687M004AT E030]	680 uF [T520D687M004AT E025]	680 uF [T520Y687M2R5AT E025]
680 uF [2R5TPF680ML]	680 uF [T510X687M006AT E023]	680 uF [T520D687M2R5AT E010]	680 uF [T525D687M003AT E025]
680 uF [4TPF680MAH]	680 uF [T513E687M006AH 6110]	680 uF [T520D687M2R5AT E015]	680 uF [T525D687M2R5AT E025]
680 uF [6TPE680M]	680 uF [T513E687M006AH 6120]	680 uF [T520D687M2R5AT E040]	680 uF [T530D687M003AT E010]
680 uF [6TPE680MI]			
680 uF [ETPF680M5H]			

Multisim 14.1 Base Edition Components

680 uF [T530D687M2R5AT E006]	680 uF [TAJE687K004RNJ]	680 uF [TPSE687K006R004 5]	680 uH [SDR0805- 681KL]
680 uF [T530D687M2R5AT E010]	680 uF [TAJE687K006RNJ]	680 uF [TPSE687K006R006 0]	680 uH [SDR0906- 681KL]
680 uF [T530X687M004AT E004]	680 uF [TPME687K004R00 18]	680 uF [TPSE687K006R010 0]	680 uH [SDR1006- 681KL]
680 uF [T530X687M004AT E006]	680 uF [TPME687K004R00 23]	680 uF [TPSV687K006R003 5]	680 uH [SDR1030- 681K]
680 uF [T530X687M004AT E010]	680 uF [TPME687K006R00 18]	680 uF [TPSV687K006R004 0]	680 uH [SDR1045- 681K]
680 uF [T530X687M006AT E010]	680 uF [TPME687K006R00 23]	680 uF [TPSV687K006R005 0]	680 uH [SDR1305- 681K]
680 uF [T530X687M006AT E018]	680 uF [TPMV687K006R00 23]	680 uF [TRME687K004R00 23]	680 uH [SDR1307- 681KL]
680 uF [T530Y687M004AT E005]	680 uF [TPSD687K004R010 0]	680 uH [SDE1006A- 681K]	680 uH [SDR1307A-681K]
680 uF [T530Y687M2R5AT E006]	680 uF [TPSE687K004R004 0]	680 uH [SDR0302- 681KL]	680 uH [SDR1806- 681KL]
680 uF [T543X687M004AT E015]	680 uF [TPSE687K004R006 0]	680 uH [SDR0403- 681KL]	680 uH [SDR6603- 681M]
680 uF [TAJC687K002RNJ]	680 uF [TPSE687K004R010 0]	680 uH [SDR0503- 681KL]	680 uH [SDR7030- 681K]
680 uF [TAJD687K004RNJ]		680 uH [SDR0604- 681KL]	680 uH [SDR7045- 681K]
		680 uH [SDR0703- 681KL]	680 uH [SRR0603- 681KL]
			680 uH [SRR0604- 681KL]

Multisim 14.1 Base Edition Components

680 uH [SRR0735A-681M]	680 uH [SRR1806-681M]	681 Ohm [CR0603-FX-6810ELF]	69.8 kOhm [CRT0603-BY-6982ELF]
680 uH [SRR0745A-681M]	680 uH [SRR5028-681Y]	681 Ohm [CR0805-FX-6810ELF]	69.8 kOhm [CRT0805-FY-6982ELF]
680 uH [SRR0805-681K]	680 uH [SRR6028-681Y]	681 Ohm [CR1206-FX-6810ELF]	69.8 Ohm [CR0201-FW-69R8GLF]
680 uH [SRR0906-681YL]	680 uH [SRR6603-681ML]	681 Ohm [CRM1206-FX-6810ELF]	69.8 Ohm [CR0402-FX-69R8GLF]
680 uH [SRR0908-681YL]	680 uH [SRR7032-681M]	681 Ohm [CRT0402-FZ-6810GLF]	69.8 Ohm [CR0603-FX-69R8ELF]
680 uH [SRR1005-681K]	680 uH [SRR7045-681M]	681 Ohm [CRT0805-FV-6810ELF]	69.8 Ohm [CR0805-FX-69R8ELF]
680 uH [SRR1205-681KL]	681 kOhm [CAY16-6813F4LF]	6.85119E+11	69.8 Ohm [CR1206-FX-69R8ELF]
680 uH [SRR1206-681KL]	681 kOhm [CR0402-FX-6813GLF]	69.8 kOhm [CR0402-FX-6982GLF]	690-009-521-900
680 uH [SRR1208-681KL]	681 kOhm [CR0603-FX-6813ELF]	69.8 kOhm [CR0603-FX-6982ELF]	698 kOhm [CR0402-FX-6983GLF]
680 uH [SRR1210-681M]	681 kOhm [CR0805-FX-6813ELF]	69.8 kOhm [CR0805-FX-6982ELF]	698 kOhm [CR0603-FX-6983ELF]
680 uH [SRR1210A-681M]	681 kOhm [CR1206-FX-6813ELF]	69.8 kOhm [CR1206-FX-6982ELF]	698 kOhm [CR0805-FX-6983ELF]
680 uH [SRR1240-681K]	681 kOhm [CRT1206-FZ-6813ELF]	69.8 kOhm [CRM2512-FX-6982ELF]	698 Ohm [CR0402-FX-6980GLF]
680 uH [SRR1260-681K]	681 Ohm [CR0402-FX-6810GLF]		
680 uH [SRR1260A-681K]			
680 uH [SRR1280-681K]			

Multisim 14.1 Base Edition Components

698 Ohm [CR0603-FX-6980ELF]	6N136-X017T	7 uH [SRR1005-7R0M]	7.4 uH [SRR6038-7R4Y]
698 Ohm [CR0805-FX-6980ELF]	6N136-X019T	7.15 kOhm [CR0402-FX-7151GLF]	7.5 kOhm [4114R-1-752]
698 Ohm [CR1206-FX-6980ELF]	6N137	7.15 kOhm [CR0603-FX-7151ELF]	7.5 kOhm [4116R-1-752]
6F6	6N137-X006	7.15 kOhm [CR0805-FX-7151ELF]	7.5 kOhm [4116R-1-752LF]
6HP04CH-TL-W	6N137-X007T	7.15 kOhm [CR1206-FX-7151ELF]	7.5 kOhm [4308R-101-752]
6J5	6N139-000E	7.15 kOhm [CR1206-FX-7151ELF]	7.5 kOhm [4308R-102-752]
6Line_Bussed	6N139-020E	7.3 uH [SRR6028-7R3Y]	7.5 kOhm [4308R-102-752LF]
6Line_Isolated	6N139-060E	7.32 kOhm [CR0402-FX-7321GLF]	7.5 kOhm [4310M-102-752]
6N1136	6N139-300E	7.32 kOhm [CR0603-FX-7321ELF]	7.5 kOhm [4310R-101-752]
6N1136-X006	6N139-320E	7.32 kOhm [CR0805-FX-7321ELF]	7.5 kOhm [4606X-102-752LF]
6N1136-X009T	6N139-360E	7.32 kOhm [CR1206-FX-7321ELF]	7.5 kOhm [4608X-102-752LF]
6N136	6POS_ROTARY	7.32 kOhm [CAY16-7501F4LF]	7.5 kOhm [CAY16-752J4LF]
6N136-000E	6SF5	7.4 uH [SRP1205-7R2Y]	
6N136-020E	7 kOhm [4116R-2-702]		
6N136-060E	7 kOhm [4816P-2-702]		
6N136-300E	7 mOhm [CRE2512-FZ-R007E-2]		
6N136-320E	7 mOhm [CRE2512-FZ-R007E-3]		
6N136-360E	7 mOhm [CRF2512-FX-R007ELF]		
6N136-X001	7 mOhm [CRF2512-JX-R007ELF]		
6N136-X006	7 Ohm [PWR6327W7R00F]		
6N136-X007T			
6N136-X009T			
6N136-X016			

Multisim 14.1 Base Edition Components

7.5 kOhm [CR0201-JW-752GLF]	7.5 kOhm [CRT0603-DY-7501ELF]	7.5 nF [C0603C752K3HACT U]	7.5 Ohm [CAT16-7R5J4LF]
7.5 kOhm [CR0402-FX-7501GLF]	7.5 kOhm [CRT0805-BY-7501ELF]	7.5 nF [C0805C752K1GACT U]	7.5 Ohm [CAY10-7R5J2LF]
7.5 kOhm [CR0402-JW-752GLF]	7.5 kOhm [CRT0805-DZ-7501ELF]	7.5 nF [C0805C752K1HACT U]	7.5 Ohm [CR0402-J/-7R5GLF]
7.5 kOhm [CR0603-FX-7501ELF]	7.5 kOhm [CRT0805-PV-7501ELF]	7.5 nF [C0805C752K5GACT U]	7.5 Ohm [CR0603-J/-7R5ELF]
7.5 kOhm [CR0603-JW-752ELF]	7.5 kOhm [PWR163S-25-7501JE]	7.5 nF [C0805C752K5HACT U]	7.5 Ohm [CR0603-J/-7R5GLF]
7.5 kOhm [CR0805-FX-7501ELF]	7.5 kOhm [PWR221T-30-7501F]	7.5 nF [C0805C752K1HACT U]	7.5 Ohm [CR0805-J/-7R5ELF]
7.5 kOhm [CR0805-JW-752ELF]	7.5 kOhm [PWR221T-30-7501J]	7.5 nF [C1206C752K3HACT U]	7.5 Ohm [CRL0603-FW-7R50ELF]
7.5 kOhm [CR1206-FX-7501ELF]	7.5 kOhm [PWR263S-35-7501JE]	7.5 nF [C1206C752K5HACT U]	7.5 Ohm [CRL0603-JW-7R50ELF]
7.5 kOhm [CR1206-JW-752ELF]	7.5 MOhm [CR0603-JW-755ELF]	7.5 nF [CDR34BP752AKSM]	7.5 Ohm [CRL0805-FW-7R50ELF]
7.5 kOhm [CR2010-FX-7501ELF]	7.5 MOhm [CR0805-JW-755ELF]	7.5 Ohm [CAT10-7R5J4LF]	7.5 Ohm [CRL0805-JW-7R50ELF]
7.5 kOhm [CRM0805-FX-7501ELF]	7.5 MOhm [CR1206-JW-755ELF]	7.5 Ohm [CAT16-7R5J4GLF]	
7.5 kOhm [CRT0402-FZ-7501GLF]			
7.5 kOhm [CRT0603-BY-7501ELF]			

Multisim 14.1 Base Edition Components

7.5 Ohm [CRL2512-FW-7R50ELF]	7.5 Ohm [PWR2010W7R50JE]	7.5 Ohm [PWR263S-35-7R50J]	7.5 uH [SRR1205-7R5ML]
7.5 Ohm [CRM1206-FX-7R50ELF]	7.5 Ohm [PWR220T-20-7R50F]	7.5 Ohm [PWR3014W7R50JE]	7.5 uH [SRR1206-7R5ML]
7.5 Ohm [CRM2010-JW-7R5ELF]	7.5 Ohm [PWR220T-20-7R50J]	7.5 Ohm [PWR4318W7R50JE]	7.5 uH [SRR1280-7R5Y]
7.5 Ohm [CRM2512-JW-7R5ELF]	7.5 Ohm [PWR220T-35-7R50J]	7.5 Ohm [PWR4525W7R50J]	7.5 uH [SRR5018-7R5Y]
7.5 Ohm [CRT0603-BY-7R50ELF]	7.5 Ohm [PWR221T-30-7R50F]	7.5 Ohm [PWR4525W7R50JE]	7.6 uH [SRR1260-7R6Y]
7.5 Ohm [FW10A7R50JA]	7.5 Ohm [PWR221T-30-7R50J]	7.5 Ohm [PWR5322W7R50JE]	7.6 uH [SRR1260A-7R6Y]
7.5 Ohm [FW20A7R50JA]	7.5 Ohm [PWR2615W7R50JE]	7.5 Ohm [PWR6327W7R50J]	7.6 uH [SRR1280-7R6Y]
7.5 Ohm [FW70A7R50JA]	7.5 Ohm [PWR263S-20-7R50F]	7.5 Ohm [PWR6327W7R50JE]	7.68 kOhm [CR0402-FX-7681GLF]
7.5 Ohm [PWR163S-25-7R50F]	7.5 Ohm [PWR263S-20-7R50J]	7.5 uH [SDR0603-7R5ML]	7.68 kOhm [CR0603-FX-7681ELF]
7.5 Ohm [PWR163S-25-7R50FE]	7.5 Ohm [PWR263S-20-7R50J]	7.5 uH [SDR0805-7R5ML]	7.68 kOhm [CR0805-FX-7681ELF]
7.5 Ohm [PWR163S-25-7R50J]	7.5 Ohm [PWR263S-20-7R50JE]	7.5 uH [SRR0804-7R5M]	7.68 kOhm [CR1206-FX-7681ELF]
7.5 Ohm [PWR1913W7R50J]	7.5 Ohm [PWR263S-35-7R50F]	7.5 uH [SRR0908-7R5ML]	7.8 uH [SRP1250-7R8M]
7.5 Ohm [PWR1913W7R50JE]		7.5 uH [SRR1003-7R5M]	7.87 kOhm [CR0402-FX-7871GLF]

Multisim 14.1 Base Edition Components

7.87 kOhm [CR0603-FX-7871ELF]	70 mOhm [CRL2512-FW-R070ELF]	715 kOhm [CR0402-FX-7153GLF]	73.2 kOhm [CR0603-FX-7322ELF]
7.87 kOhm [CR0805-FX-7871ELF]	700 mOhm [CRL0603-FW-R700ELF]	715 kOhm [CR0603-FX-7153ELF]	73.2 kOhm [CR0805-FX-7322ELF]
7.87 kOhm [CR0805-FX-7871GLF]	700 nH [SRP1206-R47Y]	715 kOhm [CR0805-FX-7153ELF]	73.2 kOhm [CR1206-FX-7322ELF]
7.87 kOhm [CR1206-FX-7871ELF]	71.5 kOhm [CR0201-FW-7152GLF]	715 kOhm [CR1206-FX-7153ELF]	73.2 Ohm [CR0805-FX-73R2ELF]
7.87 kOhm [CRM0805-FX-7871ELF]	71.5 kOhm [CR0402-FX-7152GLF]	715 Ohm [CAY16-7150F4LF]	73.2 Ohm [CR1206-FX-73R2ELF]
7.87 kOhm [CRT0402-FZ-7871GLF]	71.5 kOhm [CR0603-FX-7152ELF]	715 Ohm [CR0402-FX-7150GLF]	73.2 Ohm [CR2010-FX-73R2ELF]
7.87 kOhm [CRT0603-BX-7871ELF]	71.5 kOhm [CR0805-FX-7152ELF]	715 Ohm [CR0603-FX-7150ELF]	730 Ohm [4116R-1-731]
7.87 kOhm [CRT0603-BY-7871ELF]	71.5 kOhm [CR1206-FX-7152ELF]	715 Ohm [CR0805-FX-7150ELF]	732 kOhm [CR0402-FX-7323GLF]
7.87 Ohm [CRM2512-FX-7R87ELF]	71.5 Ohm [CR0402-FX-71R5GLF]	715 Ohm [CRT0603-BW-7150ELF]	732 kOhm [CR0805-FX-7323ELF]
70 mOhm [CRA2512-FZ-R070ELF]	71.5 Ohm [CR0603-FX-71R5ELF]	715 Ohm [CRT0805-BY-7150ELF]	732 kOhm [CR1206-FX-7323ELF]
70 mOhm [CRA2512-JZ-R070ELF]	71.5 Ohm [CR0805-FX-71R5ELF]	73.2 kOhm [CR0402-FX-7322GLF]	732 Ohm [CR0402-FX-7320GLF]
	71.5 Ohm [CR1206-FX-71R5ELF]		732 Ohm [CR0603-FX-7320ELF]

Multisim 14.1 Base Edition Components

732 Ohm [CR0805-FX-7320ELF]	74145N	74190N	7432N
	74147N	74191N	7433N
732 Ohm [CR1206-FX-7320ELF]	74148N	74192N	74365N
	7414N	74194N	74367N
732 Ohm [CRT0603-PV-7320ELF]	74150N	74195N	74368N
	74151N	74198N	7437N
73391-0060	74153N	74199N	7438N
7400N	74154N	741-DIV	74393N
7402N	74155N	7420N	7439N
7403N	74156N	7422N	7440N
7404N	74157N	74251J	7442N
7405N	74159N	74251N	7445N
7406N	74160N	7425N	7446N
7407N	74162N	7426N	7447N
7408N	74163N	74279N	7451N
7409N	74164N	7427N	7454N
741	74165N	7428N	7472N
74107N	74166N	74290N	7473N
74109N	7416N	74293N	7474N
7410N	74173N	74298N	7475N
74116N	74174N	7430N	7476N
74125N	74175N	74320-1004	7477W
74126N	7417N	74320-3004	7486N
7412N	74181J	74320-4004	749070-9
74132N	74181N	74320-5000	7490N

Multisim 14.1 Base Edition Components

7491N	74HC04N_4V	74HC107N_6V	74HC114D_2V
7492N	74HC04N_6V	74HC109D_2V	74HC114D_4V
7493N	74HC05D_2V	74HC109D_4V	74HC114D_6V
74HC00D_2V	74HC05D_4V	74HC109D_6V	74HC114N_2V
74HC00D_4V	74HC05D_6V	74HC109N_2V	74HC114N_4V
74HC00D_6V	74HC05N_2V	74HC109N_4V	74HC114N_6V
74HC00N_2V	74HC05N_4V	74HC109N_6V	74HC11D_2V
74HC00N_4V	74HC05N_6V	74HC10D_2V	74HC11D_4V
74HC00N_6V	74HC08D_2V	74HC10D_4V	74HC11D_6V
74HC02D_2V	74HC08D_4V	74HC10D_6V	74HC11N_2V
74HC02D_4V	74HC08D_6V	74HC10N_2V	74HC11N_4V
74HC02D_6V	74HC08N_2V	74HC10N_4V	74HC11N_6V
74HC02N_2V	74HC08N_4V	74HC10N_6V	74HC125N_2V
74HC02N_4V	74HC08N_6V	74HC112D_2V	74HC125N_4V
74HC02N_6V	74HC09D_2V	74HC112D_4V	74HC125N_6V
74HC03D_2V	74HC09D_4V	74HC112D_6V	74HC126N_2V
74HC03D_4V	74HC09D_6V	74HC112N_2V	74HC126N_4V
74HC03D_6V	74HC09N_2V	74HC112N_4V	74HC126N_6V
74HC03N_2V	74HC09N_4V	74HC112N_6V	74HC133D_2V
74HC03N_4V	74HC09N_6V	74HC113D_2V	74HC133D_4V
74HC03N_6V	74HC107D_2V	74HC113D_4V	74HC133D_6V
74HC04D_2V	74HC107D_4V	74HC113D_6V	74HC133D_6V
74HC04D_4V	74HC107D_6V	74HC113N_2V	74HC133N_2V
74HC04D_6V	74HC107N_2V	74HC113N_4V	74HC133N_4V
74HC04N_2V	74HC107N_4V	74HC113N_6V	74HC133N_6V

Multisim 14.1 Base Edition Components

74HC137D_2V	74HC148DW_6V	74HC154DW_2V	74HC162D_4V
74HC137D_4V	74HC148N_2V	74HC154DW_4V	74HC162D_6V
74HC137D_6V	74HC148N_4V	74HC154DW_6V	74HC162N_2V
74HC137N_2V	74HC148N_6V	74HC154NT_2V	74HC162N_4V
74HC137N_4V	74HC151D_2V	74HC154NT_4V	74HC162N_6V
74HC137N_6V	74HC151D_4V	74HC154NT_6V	74HC163D_2V
74HC138D_2V	74HC151D_6V	74HC157D_2V	74HC163D_4V
74HC138D_4V	74HC151N_2V	74HC157D_4V	74HC163D_6V
74HC138D_4V	74HC151N_4V	74HC157D_6V	74HC163N_2V
74HC138D_6V	74HC151N_6V	74HC157N_2V	74HC163N_4V
74HC138N_2V	74HC152D_2V	74HC157N_4V	74HC163N_6V
74HC138N_4V	74HC152D_4V	74HC157N_6V	74HC164N_2V
74HC138N_4V	74HC152D_6V	74HC158D_2V	74HC164N_4V
74HC138N_6V	74HC152N_2V	74HC158D_4V	74HC164N_6V
74HC139DW_2V	74HC152N_4V	74HC158D_6V	74HC165D_2V
74HC139DW_4V	74HC152N_6V	74HC158N_2V	74HC165D_4V
74HC139DW_6V	74HC153D_2V	74HC158N_4V	74HC165D_6V
74HC139N_2V	74HC153D_4V	74HC158N_6V	74HC165N_2V
74HC139N_4V	74HC153D_6V	74HC160D_2V	74HC165N_4V
74HC139N_6V	74HC153DW_2V	74HC160D_4V	74HC165N_6V
74HC147N_2V	74HC153DW_4V	74HC160D_6V	74HC166D_2V
74HC147N_4V	74HC153DW_6V	74HC160N_2V	74HC166D_4V
74HC147N_6V	74HC153N_2V	74HC160N_4V	74HC166D_6V
74HC148DW_2V	74HC153N_4V	74HC160N_6V	74HC166N_2V
74HC148DW_4V	74HC153N_6V	74HC162D_2V	74HC166N_4V

Multisim 14.1 Base Edition Components

74HC166N_6V	74HC191D_2V	74HC21D_4V	74HC251D_4V
74HC173D_2V	74HC191D_4V	74HC21D_6V	74HC251D_6V
74HC173D_4V	74HC191D_6V	74HC21N_2V	74HC251N_2V
74HC173D_6V	74HC191N_2V	74HC21N_4V	74HC251N_4V
74HC173N_2V	74HC191N_4V	74HC21N_6V	74HC251N_6V
74HC173N_4V	74HC191N_6V	74HC240DW_2V	74HC253D_2V
74HC173N_6V	74HC192D_2V	74HC240DW_4V	74HC253D_4V
74HC174D_2V	74HC192D_4V	74HC240DW_6V	74HC253D_6V
74HC174D_4V	74HC192D_6V	74HC240N_2V	74HC253N_2V
74HC174D_6V	74HC192N_2V	74HC240N_4V	74HC253N_4V
74HC174N_2V	74HC192N_4V	74HC240N_6V	74HC253N_6V
74HC174N_4V	74HC192N_6V	74HC241DW_2V	74HC257D_2V
74HC174N_6V	74HC194N_2V	74HC241DW_4V	74HC257D_4V
74HC175D_2V	74HC194N_4V	74HC241DW_6V	74HC257D_6V
74HC175D_4V	74HC194N_6V	74HC241N_2V	74HC257N_2V
74HC175D_6V	74HC195N_2V	74HC241N_4V	74HC257N_4V
74HC175N_2V	74HC195N_4V	74HC241N_6V	74HC257N_6V
74HC175N_4V	74HC195N_6V	74HC244_4V	74HC258D_2V
74HC175N_6V	74HC20D_2V	74HC244DW_2V	74HC258D_4V
74HC190D_2V	74HC20D_4V	74HC244DW_4V	74HC258D_6V
74HC190D_4V	74HC20D_6V	74HC244DW_6V	74HC258N_2V
74HC190D_6V	74HC20N_2V	74HC244N_2V	74HC258N_4V
74HC190N_2V	74HC20N_4V	74HC244N_4V	74HC258N_6V
74HC190N_4V	74HC20N_6V	74HC244N_6V	74HC266D_2V
74HC190N_6V	74HC21D_2V	74HC251D_2V	74HC266D_4V

Multisim 14.1 Base Edition Components

74HC266D_6V	74HC283N_2V	74HC366D_6V	74HC374N_4V
74HC266N_2V	74HC283N_4V	74HC366N_2V	74HC374N_6V
74HC266N_4V	74HC283N_6V	74HC366N_6V	74HC375D_2V
74HC266N_6V	74HC298N_2V	74HC367D_2V	74HC375D_4V
74HC273DW_2V	74HC298N_4V	74HC367D_4V	74HC375D_6V
74HC273DW_4V	74HC298N_6V	74HC367D_6V	74HC375N_2V
74HC273DW_6V	74HC30D_2V	74HC367N_2V	74HC375N_4V
74HC273N_2V	74HC30D_4V	74HC367N_4V	74HC375N_6V
74HC273N_4V	74HC30D_6V	74HC367N_6V	74HC377DW_2V
74HC273N_6V	74HC30N_2V	74HC368D_2V	74HC377DW_4V
74HC27D_2V	74HC30N_4V	74HC368D_4V	74HC377DW_6V
74HC27D_4V	74HC30N_6V	74HC368D_6V	74HC377N_2V
74HC27D_6V	74HC32D_2V	74HC368N_2V	74HC377N_4V
74HC27N_2V	74HC32D_4V	74HC368N_4V	74HC377N_6V
74HC27N_4V	74HC32D_6V	74HC368N_6V	74HC378D_2V
74HC27N_6V	74HC32N_2V	74HC373DW_2V	74HC378D_4V
74HC280D_2V	74HC32N_4V	74HC373DW_4V	74HC378D_6V
74HC280D_4V	74HC32N_6V	74HC373DW_6V	74HC378N_2V
74HC280D_6V	74HC365D_2V	74HC373N_2V	74HC378N_4V
74HC280N_2V	74HC365D_4V	74HC373N_4V	74HC378N_6V
74HC280N_4V	74HC365D_6V	74HC373N_6V	74HC379D_2V
74HC280N_6V	74HC365N_2V	74HC374DW_2V	74HC379D_4V
74HC283D_2V	74HC365N_4V	74HC374DW_4V	74HC379D_6V
74HC283D_4V	74HC365N_6V	74HC374DW_6V	74HC379J_2V
74HC283D_6V	74HC366D_2V	74HC374N_2V	74HC379J_4V

Multisim 14.1 Base Edition Components

74HC379J_6V	74HC74D_2V	74HC78D_4V	74LS04N
74HC379N_2V	74HC74D_4V	74HC78D_6V	74LS04N
74HC379N_4V	74HC74D_6V	74HC78N_2V	74LS05D
74HC379N_6V	74HC74N_2V	74HC78N_4V	74LS05D
74HC393N_2V	74HC74N_4V	74HC78N_6V	74LS05N
74HC393N_4V	74HC74N_6V	74HC86D_2V	74LS05N
74HC393N_6V	74HC75D_2V	74HC86D_4V	74LS08D
74HC42D_2V	74HC75D_4V	74HC86D_6V	74LS08D
74HC42D_4V	74HC75D_6V	74HC86N_2V	74LS08J
74HC42D_6V	74HC75N_2V	74HC86N_4V	74LS08J
74HC42N_2V	74HC75N_4V	74HC86N_6V	74LS08N
74HC42N_4V	74HC75N_6V	74LS00D	74LS08N
74HC42N_6V	74HC76D_2V	74LS00D	74LS09D
74HC51D_2V	74HC76D_4V	74LS00N	74LS09D
74HC51D_4V	74HC76D_6V	74LS00N	74LS09N
74HC51D_6V	74HC76N_2V	74LS02D	74LS09N
74HC51N_2V	74HC76N_4V	74LS02D	74LS107D
74HC51N_4V	74HC76N_6V	74LS02N	74LS107D
74HC51N_6V	74HC77D_2V	74LS02N	74LS107N
74HC73D_2V	74HC77D_4V	74LS03D	74LS107N
74HC73D_4V	74HC77D_6V	74LS03D	74LS109D
74HC73D_6V	74HC77N_2V	74LS03N	74LS109D
74HC73N_2V	74HC77N_4V	74LS03N	74LS109N
74HC73N_4V	74HC77N_6V	74LS04D	74LS109N
74HC73N_6V	74HC78D_2V	74LS04D	74LS10D

Multisim 14.1 Base Edition Components

74LS10D	74LS12D	74LS148N	74LS158N
74LS10N	74LS12D	74LS14D	74LS158N
74LS10N	74LS12N	74LS14N	74LS15D
74LS112D	74LS12N	74LS151D	74LS15D
74LS112D	74LS132D	74LS151D	74LS15N
74LS112N	74LS132N	74LS151N	74LS15N
74LS112N	74LS138D	74LS151N	74LS160D
74LS113D	74LS138D	74LS153D	74LS160D
74LS113D	74LS138N	74LS153D	74LS160N
74LS113N	74LS138N	74LS153N	74LS160N
74LS113N	74LS139D	74LS153N	74LS162D
74LS114D	74LS139D	74LS155D	74LS162D
74LS114D	74LS139N	74LS155D	74LS162N
74LS114N	74LS139N	74LS155N	74LS162N
74LS114N	74LS145D	74LS155N	74LS163D
74LS11D	74LS145D	74LS156D	74LS163D
74LS11D	74LS145N	74LS156D	74LS163N
74LS11N	74LS145N	74LS156N	74LS163N
74LS11N	74LS147D	74LS156N	74LS164D
74LS125D	74LS147D	74LS157D	74LS164D
74LS125D	74LS147N	74LS157D	74LS164N
74LS125N	74LS147N	74LS157N	74LS164N
74LS126D	74LS148D	74LS157N	74LS165D
74LS126D	74LS148D	74LS158D	74LS165D
74LS126N	74LS148N	74LS158D	74LS165N

Multisim 14.1 Base Edition Components

74LS165N	74LS190D	74LS21D	74LS257D
74LS166D	74LS190D	74LS21N	74LS257D
74LS166D	74LS190N	74LS21N	74LS257N
74LS166N	74LS190N	74LS22D	74LS257N
74LS166N	74LS191D	74LS22D	74LS258D
74LS169D	74LS191D	74LS22N	74LS258D
74LS169D	74LS191N	74LS22N	74LS258N
74LS169N	74LS191N	74LS240DW	74LS258N
74LS169N	74LS192D	74LS240DW	74LS266D
74LS173D	74LS192D	74LS240N	74LS266D
74LS173D	74LS192N	74LS240N	74LS266N
74LS173N	74LS192N	74LS241DW	74LS266N
74LS173N	74LS194D	74LS241DW	74LS26D
74LS174D	74LS194D	74LS241N	74LS26D
74LS174D	74LS194N	74LS241N	74LS26N
74LS174N	74LS194N	74LS244DW	74LS26N
74LS174N	74LS195D	74LS244N	74LS273DW
74LS175D	74LS195D	74LS251D	74LS273DW
74LS175D	74LS195N	74LS251D	74LS273N
74LS175N	74LS195N	74LS251N	74LS273N
74LS175N	74LS20D	74LS251N	74LS279D
74LS181DW	74LS20D	74LS253D	74LS279N
74LS181DW	74LS20N	74LS253D	74LS27D
74LS181N	74LS20N	74LS253N	74LS27D
74LS181N	74LS21D	74LS253N	74LS27N

Multisim 14.1 Base Edition Components

74LS27N	74LS32D	74LS368D	74LS37D
74LS280D	74LS32N	74LS368N	74LS37D
74LS280D	74LS32N	74LS368N	74LS37N
74LS280N	74LS33D	74LS373DW	74LS38D
74LS280N	74LS33D	74LS373DW	74LS38D
74LS28D	74LS33N	74LS373N	74LS38N
74LS28D	74LS33N	74LS373N	74LS38N
74LS28N	74LS348D	74LS374DW	74LS393D
74LS28N	74LS348N	74LS374DW	74LS393D
74LS290D	74LS352D	74LS374N	74LS393N
74LS290D	74LS352D	74LS374N	74LS393N
74LS290N	74LS352N	74LS375D	74LS395D
74LS290N	74LS352N	74LS375N	74LS395D
74LS293D	74LS353D	74LS377DW	74LS395N
74LS293D	74LS353D	74LS377DW	74LS395N
74LS293N	74LS353N	74LS377N	74LS399D
74LS293N	74LS365D	74LS377N	74LS399N
74LS298D	74LS365D	74LS378D	74LS40D
74LS298D	74LS365N	74LS378D	74LS40D
74LS298N	74LS365N	74LS378N	74LS40N
74LS298N	74LS367D	74LS378N	74LS40N
74LS30D	74LS367D	74LS379D	74LS42D
74LS30N	74LS367N	74LS379D	74LS42D
74LS30N	74LS367N	74LS379N	74LS42N
74LS32D	74LS368D	74LS379N	74LS42N

Multisim 14.1 Base Edition Components

74LS445D	74LS541N	74LS76D	74LS92N
74LS445D	74LS54D	74LS76D	74LS93D
74LS445N	74LS54D	74LS76N	74LS93D
74LS445N	74LS54N	74LS76N	74LS93N
74LS465DW	74LS54N	74LS77W	74LS93N
74LS465DW	74LS55D	74LS77W	74STD06N
74LS465N	74LS55D	74LS78D	74STD07N
74LS465N	74LS55N	74LS78D	74STD116N
74LS466DW	74LS55N	74LS78N	74STD150N
74LS466DW	74LS69D	74LS78N	74STD154N
74LS466N	74LS69D	74LS86D	74STD159N
74LS466N	74LS69N	74LS86D	74STD16N
74LS47D	74LS69N	74LS86N	74STD17N
74LS47D	74LS73D	74LS86N	74STD198N
74LS47N	74LS73D	74LS90D	74STD199N
74LS47N	74LS73N	74LS90D	74STD25N
74LS48D	74LS73N	74LS90N	74STD39N
74LS48N	74LS74D	74LS90N	74STD45N
74LS51D	74LS74D	74LS91D	74STD72N
74LS51D	74LS74N	74LS91D	75 kOhm [4114R-1-753]
74LS51N	74LS74N	74LS91N	75 kOhm [4114R-1-753LF]
74LS51N	74LS75D	74LS91N	75 kOhm [4608X-102-753LF]
74LS540DW	74LS75D	74LS92D	
74LS540N	74LS75N	74LS92D	
74LS541DW	74LS75N	74LS92N	

Multisim 14.1 Base Edition Components

75 kOhm [4816P-1-753F]	75 kOhm [CRT0603-FZ-7502ELF]	75 Ohm [4114R-1-750]	75 Ohm [4606X-102-750LF]
75 kOhm [4816P-2-753]	75 kOhm [CRT0805-BW-7502ELF]	75 Ohm [4116R-1-750]	75 Ohm [4608X-101-750LF]
75 kOhm [4816P-2-753LF]	75 kOhm [CRT0805-DY-7502ELF]	75 Ohm [4116R-1-750LF]	75 Ohm [4608X-102-750LF]
75 kOhm [CAY16-753J4LF]	75 kOhm [CRT0805-DY-7502ELF]	75 Ohm [4306R-101-750]	75 Ohm [4610X-101-750LF]
75 kOhm [CR0402-FX-7502GLF]	75 mF [C0805C759KBGAC TU]	75 Ohm [4308H-101-750]	75 Ohm [4610X-102-750LF]
75 kOhm [CR0402-JW-753GLF]	75 mOhm [CRA2512-FZ-R075ELF]	75 Ohm [4308R-101-750]	75 Ohm [4613X-101-750LF]
75 kOhm [CR0603-FX-7502ELF]	75 mOhm [CRA2512-JZ-R075ELF]	75 Ohm [4308R-101-750LF]	75 Ohm [4816P-1-750]
75 kOhm [CR0603-JW-753ELF]	75 mOhm [CRM2512-FX-R075ELF]	75 Ohm [4308R-102-750]	75 Ohm [4816P-1-750LF]
75 kOhm [CR0805-FX-7502ELF]	75 mOhm [PWR163S-25-R075J]	75 Ohm [4308R-102-750LF]	75 Ohm [4816P-T01-750]
75 kOhm [CR0805-JW-753ELF]	75 mOhm [PWR163S-25-R075JE]	75 Ohm [4310R-101-750]	75 Ohm [CAT10-750J4LF]
75 kOhm [CR1206-FX-7502ELF]	75 mOhm [PWR220T-20-R075J]	75 Ohm [4310R-101-750LF]	75 Ohm [CAT16-750J2LF]
75 kOhm [CR1206-JW-753ELF]	75 mOhm [PWR221T-30-R075J]	75 Ohm [4416P-1-750]	75 Ohm [CAT16-750J4LF]
75 kOhm [CR1206-JW-753GLF]		75 Ohm [4604X-101-750LF]	75 Ohm [CAT16-75R0F4LF]
75 kOhm [CRM2512-FX-7502ELF]		75 Ohm [4605X-101-750LF]	75 Ohm [CAT25-750JALF]
75 kOhm [CRT0402-FZ-7502GLF]		75 Ohm [4606X-101-750LF]	75 Ohm [CAY10-750J2LF]

Multisim 14.1 Base Edition Components

75 Ohm [CAY10-750J4LF]	75 Ohm [CR2010-JW-750ELF]	75 Ohm [PWR220T-20-75R0J]	75 Ohm [PWR5322W75R0JE]
75 Ohm [CAY16-750J4LF]	75 Ohm [CR2512-FX-75R0ELF]	75 Ohm [PWR220T-35-75R0J]	75 Ohm [PWR6327W75R0J]
75 Ohm [CAY16-75R0F4LF]	75 Ohm [CR2512-JW-750ELF]	75 Ohm [PWR221T-30-75R0F]	75 pF [C0603C750K5GACT U]
75 Ohm [CAY17-750JALF]	75 Ohm [CRM1206-FX-75R0ELF]	75 Ohm [PWR221T-30-75R0J]	75 pF [C0805C750K2GACT U]
75 Ohm [CR0402-FX-75R0GLF]	75 Ohm [CRM2512-FX-75R0ELF]	75 Ohm [PWR263S-20-75R0F]	75 pF [C0805C750KBGAC TU]
75 Ohm [CR0402-JW-750GLF]	75 Ohm [CRT0402-FZ-75R0GLF]	75 Ohm [PWR263S-20-75R0J]	75 pF [C0805C750KCGAC TU]
75 Ohm [CR0603-FX-75R0ELF]	75 Ohm [CRT0805-BY-75R0ELF]	75 Ohm [PWR263S-35-75R0F]	75 pF [C1206C750K5GACT U]
75 Ohm [CR0603-JW-750ELF]	75 Ohm [PWR163S-25-75R0F]	75 Ohm [PWR263S-35-75R0J]	75 pF [C1206C750KBGAC TU]
75 Ohm [CR0603-JW-750GLF]	75 Ohm [PWR163S-25-75R0FE]	75 Ohm [PWR3014W75R0JE]	75 pF [C1812C750KBGAC TU]
75 Ohm [CR0805-FX-75R0ELF]	75 Ohm [PWR163S-25-75R0J]	75 Ohm [PWR4318W75R0JE]	75 pF [C1825C750KBGAC TU]
75 Ohm [CR0805-FX-75R0GLF]	75 Ohm [PWR163S-25-75R0JE]	75 Ohm [PWR4525W75R0J]	
75 Ohm [CR0805-JW-750ELF]	75 Ohm [PWR220T-20-75R0F]		
75 Ohm [CR0805-JW-750GLF]			
75 Ohm [CR1206-FX-75R0ELF]			
75 Ohm [CR1206-JW-750ELF]			

Multisim 14.1 Base Edition Components

75 pF [C2220C750KBGAC TU]	750 kOhm [CR1206-FX- 7503ELF]	750 mOhm [CRM2512-FX- R750ELF]	750 mOhm [PWR263S-20- R750F]
75 pF [C2225C750KBGAC TU]	750 kOhm [CR1206-JW- 754ELF]	750 mOhm [CRM2512-JX- R750ELF]	750 mOhm [PWR263S-20- R750J]
75 uH [SRR1205- 750YL]	750 kOhm [CRT0805-BY- 7503ELF]	750 mOhm [PWR163S-25- R750F]	750 mOhm [PWR263S-35- R750F]
750 kOhm [4816P- 1-754]	750 mOhm [CRL0603-FW- R750ELF]	750 mOhm [PWR163S-25- R750FE]	750 mOhm [PWR263S-35- R750J]
750 kOhm [CAY16- 754J4LF]	750 mOhm [CRL0603-JW- R750ELF]	750 mOhm [PWR163S-25- R750J]	750 mOhm [PWR3014WR750JE]
750 kOhm [CHV0805-FX- 7503ELF]	750 mOhm [CRL0805-FW- R750ELF]	750 mOhm [PWR1913WR750J]	750 mOhm [PWR4318WR750JE]
750 kOhm [CR0402-FX- 7503GLF]	750 mOhm [CRL0805-JW- R750ELF]	750 mOhm [PWR1913WR750JE]	750 mOhm [PWR4525WR750F]
750 kOhm [CR0402-JW- 754GLF]	750 mOhm [CRL1206-FW- R750ELF]	750 mOhm [PWR2010WR750JE]	750 mOhm [PWR4525WR750F E]
750 kOhm [CR0603-FX- 7503ELF]	750 mOhm [CRL1206-JW- R750ELF]	750 mOhm [PWR220T-20- R750F]	750 mOhm [PWR4525WR750J]
750 kOhm [CR0603-JW- 754ELF]	750 mOhm [CRL2010-FW- R750ELF]	750 mOhm [PWR220T-20- R750J]	750 mOhm [PWR4525WR750JE]
750 kOhm [CR0805-FX- 7503ELF]	750 mOhm [CRL2010-JW- R750ELF]	750 mOhm [PWR2615WR750J]	750 mOhm [PWR5322WR750JE]
750 kOhm [CR0805-JW- 754ELF]		750 mOhm [PWR2615WR750JE]	750 mOhm [PWR6327WR750J]

Multisim 14.1 Base Edition Components

750 mOhm [PWR6327WR750JE]	750 Ohm [4310R- 101-751]	750 Ohm [CR0603- FX-7500ELF]	750 Ohm [PWR163S-25- 7500FE]
750 nH [SRP1040- R75M]	750 Ohm [4310R- 101-751LF]	750 Ohm [CR0603- JW-751ELF]	750 Ohm [PWR263S-35- 7500F]
750 nH [SRP1204- R50M]	750 Ohm [4606X- 101-751LF]	750 Ohm [CR0805- FX-7500ELF]	750 Ohm [PWR263S-35- 7500FE]
750 nH [SRP7028A- R75M]	750 Ohm [4608X- 102-751LF]	750 Ohm [CR0805- JW-751ELF]	750 pF [C0402C751K1HACT U]
750 Ohm [4114R-1- 751]	750 Ohm [4609M- 101-751LF]	750 Ohm [CR1206- FX-7500ELF]	750 pF [C0402C751K3HACT U]
750 Ohm [4114R-2- 751]	750 Ohm [4610X- 101-751LF]	750 Ohm [CR1206- JW-751ELF]	750 pF [C0402C751K5HACT U]
750 Ohm [4116R-1- 751]	750 Ohm [4816P-1- 751]	750 Ohm [CR2512- FX-7500ELF]	750 pF [C0603C751K1HACT U]
750 Ohm [4116R-1- 751LF]	750 Ohm [4816P-1- 751LF]	750 Ohm [CR2512- JW-751ELF]	750 pF [C0603C751K3HACT U]
750 Ohm [4116R-2- 751]	750 Ohm [4816P- T01-751]	750 Ohm [CRM1206-FX- 7500ELF]	750 pF [C0603C751K5HACT U]
750 Ohm [4306H- 102-751]	750 Ohm [CAT16- 7500F4LF]	750 Ohm [CRM2512-FX- 7500ELF]	750 pF [C0603C751K3HACT U]
750 Ohm [4306R- 102-751]	750 Ohm [CAT16- 751J4LF]	750 Ohm [CRT0402-FZ- 7500GLF]	750 pF [C0603C751K5GACT U]
750 Ohm [4308H- 101-751]	750 Ohm [CAY16- 7500F4LF]	750 Ohm [CRT0603-BY- 7500ELF]	750 pF [C1210C751KBGAC TU]
750 Ohm [4308H- 101-751LF]	750 Ohm [CAY16- 751J4LF]	750 Ohm [CRT0603-FY- 7500ELF]	
750 Ohm [4308R- 102-751]	750 Ohm [CR0402- FX-7500GLF]		
750 Ohm [4308R- 102-751LF]	750 Ohm [CR0402- JW-751GLF]		

Multisim 14.1 Base Edition Components

750 pF [C1812C751KBGAC TU]	76.8 Ohm [CR0603- FX-76R8ELF]	768 Ohm [CRT0402-BW- 7680GLF]	787 kOhm [CR0402-FX- 7873GLF]
750 pF [C1825C751KBGAC TU]	76.8 Ohm [CR0805- FX-76R8ELF]	777778-01	787 kOhm [CR0603-FX- 7873ELF]
750 pF [C2220C751KBGAC TU]	76.8 Ohm [CR0805- FX-76R8GLF]	777779-01	787 kOhm [CR0805-FX- 7873ELF]
750 pF [C2225C751KBGAC TU]	76.8 Ohm [CR1206- FX-76R8ELF]	779157-01	787 kOhm [CR0805-FX- 7873ELF]
750 pF [C2225C751KBGAC TU]	768 kOhm [CR0402-FX- 7683GLF]	78.7 kOhm [CR0402-FX- 7872GLF]	787 kOhm [CR1206-FX- 7873ELF]
750 uOhm [CST0612-FC- R00075E]	768 kOhm [CR0603-FX- 7683ELF]	78.7 kOhm [CR0603-FX- 7872ELF]	787 Ohm [CR0402- FX-7870GLF]
76.8 kOhm [CR0201-FW- 7682GLF]	768 kOhm [CR0805-FX- 7683ELF]	78.7 kOhm [CR0805-FX- 7872ELF]	787 Ohm [CR0603- FX-7870ELF]
76.8 kOhm [CR0402-FX- 7682GLF]	768 kOhm [CR1206-FX- 7683ELF]	78.7 kOhm [CR1206-FX- 7872ELF]	787 Ohm [CR0805- FX-7870ELF]
76.8 kOhm [CR0603-FX- 7682ELF]	768 Ohm [CR0402- FX-7680GLF]	78.7 kOhm [CRT0402-FZ- 7872GLF]	787 Ohm [CR1206- FX-7870ELF]
76.8 kOhm [CR0603-FX- 7682GLF]	768 Ohm [CR0603- FX-7680ELF]	78.7 Ohm [CR0402- FX-78R7GLF]	787 Ohm [CRM2512-FX- 7870ELF]
76.8 kOhm [CR0805-FX- 7682ELF]	768 Ohm [CR0805- FX-7680ELF]	78.7 Ohm [CR0603- FX-78R7ELF]	7Line_Bussed
76.8 kOhm [CR1206-FX- 7682ELF]	768 Ohm [CR1206- FX-7680ELF]	78.7 Ohm [CR0805- FX-78R7ELF]	7Line_Isolated
76.8 kOhm [CRM2512-FX- 7680ELF]	768 Ohm [CRM2512-FX- 7680ELF]	78.7 Ohm [CR1206- FX-78R7ELF]	7POS_ROTARY
		781334-01	8 kOhm [4116R-1- 802]
			8 kOhm [4116R-1- 802LF]
			8 kOhm [4816P- T02-802]

Multisim 14.1 Base Edition Components

8 kOhm [PWR4525W8001J]	8.06 kOhm [CRT0603-BY- 8061ELF]	8.2 kOhm [4308R- 101-822LF]	8.2 kOhm [4416P- T01-822LF]
8 mOhm [CRE2512- FZ-R008E-2]	8.06 kOhm [CRT0603-CY- 8061ELF]	8.2 kOhm [4308R- 102-822]	8.2 kOhm [4420P- T01-822]
8 mOhm [CRE2512- FZ-R008E-3]	8.2 kOhm [4114R- 1-822]	8.2 kOhm [4308R- 102-822LF]	8.2 kOhm [4604X- 101-822LF]
8 mOhm [CRF2512- FX-R008ELF]	8.2 kOhm [4114R- 1-822LF]	8.2 kOhm [4309R- 101-822]	8.2 kOhm [4604X- 102-822LF]
8 Ohm [4608M- 102-8R0LF]	8.2 kOhm [4114R- 2-822]	8.2 kOhm [4309R- 101-822LF]	8.2 kOhm [4605X- 101-822LF]
8 Ohm [PWR163S- 25-8R00F]	8.2 kOhm [4116R- 1-822]	8.2 kOhm [4310M- 101-822]	8.2 kOhm [4606X- 101-822LF]
8 Ohm [PWR163S- 25-8R00FE]	8.2 kOhm [4116R- 1-822LF]	8.2 kOhm [4310M- 101-822LF]	8.2 kOhm [4606X- 102-822LF]
8 Ohm [PWR220T- 35-8R00F]	8.2 kOhm [4116R- 2-822]	8.2 kOhm [4310R- 101-822]	8.2 kOhm [4607X- 101-822LF]
8 Ohm [PWR221T- 30-8R00F]	8.2 kOhm [4116R- 2-822LF]	8.2 kOhm [4310R- 101-822LF]	8.2 kOhm [4608H- 102-822LF]
8 Ohm [PWR263S- 35-8R00F]	8.2 kOhm [4306R- 101-822]	8.2 kOhm [4310R- 102-822]	8.2 kOhm [4608M- 101-822LF]
8.06 kOhm [CR0402-FX- 8061GLF]	8.2 kOhm [4306R- 101-822LF]	8.2 kOhm [4310R- 102-822LF]	8.2 kOhm [4608X- 101-822LF]
8.06 kOhm [CR0603-FX- 8061ELF]	8.2 kOhm [4306R- 102-822]	8.2 kOhm [4416P- 1-822]	8.2 kOhm [4608X- 102-822LF]
8.06 kOhm [CR0805-FX- 8061ELF]	8.2 kOhm [4306R- 102-822LF]	8.2 kOhm [4416P- 2-822LF]	8.2 kOhm [4609X- 101-822LF]
8.06 kOhm [CR1206-FX- 8061ELF]	8.2 kOhm [4308H- 102-822LF]	8.2 kOhm [4416P- T01-822]	8.2 kOhm [4610X- 102-822LF]

Multisim 14.1 Base Edition Components

8.2 kOhm [4612X-102-822LF]	8.2 kOhm [4820P-T02-822]	8.2 kOhm [CR0805-FX-8201ELF]	8.2 mH [SDR1005-822KL]
8.2 kOhm [4614X-102-822LF]	8.2 kOhm [CAT10-822J4LF]	8.2 kOhm [CR0805-JW-822ELF]	8.2 mH [SRR0906-822YL]
8.2 kOhm [4814P-2-822]	8.2 kOhm [CAT16-8201F4LF]	8.2 kOhm [CR1206-FX-8201ELF]	8.2 mH [SRR0908-822YL]
8.2 kOhm [4814P-2-822LF]	8.2 kOhm [CAT16-822J4LF]	8.2 kOhm [CR1206-JW-822ELF]	8.2 mH [SRR1208-822KL]
8.2 kOhm [4814P-T02-822]	8.2 kOhm [CAT16-822J8LF]	8.2 kOhm [CR2010-JW-822ELF]	8.2 MOhm [4604X-102-825LF]
8.2 kOhm [4814P-T02-822LF]	8.2 kOhm [CAT25-822JALF]	8.2 kOhm [CR2512-JW-822ELF]	8.2 MOhm [CAT25-825JALF]
8.2 kOhm [4816P-1-822]	8.2 kOhm [CAY10-822J4LF]	8.2 kOhm [CRM1206-JW-822ELF]	8.2 MOhm [CR0603-JW-825ELF]
8.2 kOhm [4816P-1-822LF]	8.2 kOhm [CAY16-8201F4LF]	8.2 kOhm [CRM2512-JW-822ELF]	8.2 MOhm [CR0805-JW-825ELF]
8.2 kOhm [4816P-2-822]	8.2 kOhm [CAY16-822J4LF]	8.2 kOhm [CRT0603-BY-8201ELF]	8.2 MOhm [CR1206-JW-825ELF]
8.2 kOhm [4816P-2-822LF]	8.2 kOhm [CAY16-822J8LF]	8.2 kOhm [CRT0603-FY-8201ELF]	8.2 nF [C0402C822K3RACT U]
8.2 kOhm [4816P-T01-822]	8.2 kOhm [CAY17-822JALF]	8.2 kOhm [PWR163S-25-8201FE]	8.2 nF [C0402C822K4RACT U]
8.2 kOhm [4816P-T01-822LF]	8.2 kOhm [CR0402-FX-8201GLF]	8.2 mH [SDR0503-822JL]	8.2 nF [C0402C822K5RACT U]
8.2 kOhm [4816P-T02-822]	8.2 kOhm [CR0402-JW-822GLF]	8.2 mH [SDR0906-822KL]	8.2 nF [C0402C822K9RACT U]
8.2 kOhm [4816P-T02-822LF]	8.2 kOhm [CR0603-FX-8201ELF]		
8.2 kOhm [4820P-2-822]	8.2 kOhm [CR0603-JW-822ELF]		

Multisim 14.1 Base Edition Components

8.2 nF [C0603C822K1RACT U]	8.2 nF [C0805C822K3HACT U]	8.2 nF [C1206C822K5RACT U]	8.2 nF [GMC7.3822K100K3 1TR12]
8.2 nF [C0603C822K3GACT U]	8.2 nF [C0805C822K3RACT U]	8.2 nF [C1206C822KARACT U]	8.2 nF [GMC7.3822K400K3 5TR12]
8.2 nF [C0603C822K3HACT U]	8.2 nF [C0805C822K4RACT U]	8.2 nF [C1210C822K5GACT U]	8.2 nF [GMC7.3822K63K31 TR12]
8.2 nF [C0603C822K3RACT U]	8.2 nF [C0805C822K5GACT U]	8.2 nF [C1210C822K5RACT U]	8.2 nF [GMC7.3823K100K3 5TR12]
8.2 nF [C0603C822K4RACT U]	8.2 nF [C0805C822K5HACT U]	8.2 nF [C1210C822KARACT U]	8.2 nF [MMC5.7822K100J 31TR12]
8.2 nF [C0603C822K5RACT U]	8.2 nF [C0805C822K5RACT U]	8.2 nF [C1812C822K5GACT U]	8.2 nF [MMC5.7822K250J 31TR12]
8.2 nF [C0805C822K1GACT U]	8.2 nF [C1206C822K1HACT U]	8.2 nF [C1812C822K5RACT U]	8.2 nF [MMC5.7822K50J3 1TR12]
8.2 nF [C0805C822K1HACT U]	8.2 nF [C1206C822K1RACT U]	8.2 nF [C2220C822K2GACT U]	8.2 nF [MMC7.3822K100K 31TR12]
8.2 nF [C0805C822K1RACT U]	8.2 nF [C1206C822K2RACT U]	8.2 nF [GMC5.7822K100J3 1TR12]	8.2 nF [MMC7.3822K250K 31TR12]
8.2 nF [C0805C822K2RACT U]	8.2 nF [C1206C822K3HACT U]	8.2 nF [GMC5.7822K250J3 1TR12]	8.2 nF [MMC7.3822K400K 33TR12]
8.2 nF [C0805C822K3GACT U]	8.2 nF [C1206C822K5HACT U]	8.2 nF [GMC5.7822K50J31 TR12]	8.2 nF [MMC7.3822K50K3 1TR12]

Multisim 14.1 Base Edition Components

8.2 nF [MMC7.3822K63K3 1TR12]	8.2 Ohm [CRL2512- FW-8R20ELF]	8.2 Ohm [PWR263S-20- 8R20FE]	8.2 uF [MDC10825K100A5 8P7TUBE]
8.2 Ohm [CR0402- J/-8R2GLF]	8.2 Ohm [CRM2512-JW- 8R2ELF]	8.2 Ohm [PWR263S-20- 8R20J]	8.2 uF [MDC10825K100A5 8P8TUBE]
8.2 Ohm [CR0603- J/-8R2ELF]	8.2 Ohm [FW10A8R20JA]	8.2 Ohm [PWR263S-35- 8R20F]	8.2 uF [MDC10825K50A57 P7TUBE]
8.2 Ohm [CR0805- J/-8R2ELF]	8.2 Ohm [FW20A8R20JA]	8.2 uF [20TQC8R2M]	8.2 uF [MDC10825K50A57 P8TUBE]
8.2 Ohm [CR1206- J/-8R2ELF]	8.2 Ohm [FW30A8R20JA]	8.2 uF [A700V825M016AT E045]	8.2 uH [SDE0403A- 8R2M]
8.2 Ohm [CR1206- JW-8R2ELF]	8.2 Ohm [PWR163S-25- 8R20F]	8.2 uF [C1206C825K4PACT U]	8.2 uH [SDE0604A- 8R2M]
8.2 Ohm [CR2512- J/-8R2ELF]	8.2 Ohm [PWR163S-25- 8R20J]	8.2 uF [C1206C825K8PACT U]	8.2 uH [SDE0805A- 8R2M]
8.2 Ohm [CRL0603- FW-8R20ELF]	8.2 Ohm [PWR220T-20- 8R20F]	8.2 uF [C1206C825K8RACT U]	8.2 uH [SDE1006A- 8R2M]
8.2 Ohm [CRL0603- JW-8R20ELF]	8.2 Ohm [PWR220T-20- 8R20J]	8.2 uF [C1206C825K9RACT U]	8.2 uH [SDR0302- 8R2ML]
8.2 Ohm [CRL0805- FW-8R20ELF]	8.2 Ohm [PWR221T-30- 8R20F]	8.2 uF [C1210C825K3PACT U]	8.2 uH [SDR0403- 8R2ML]
8.2 Ohm [CRL0805- JW-8R20ELF]	8.2 Ohm [PWR221T-30- 8R20J]	8.2 uF [C1210C825K4PACT U]	8.2 uH [SDR0604- 8R2ML]
8.2 Ohm [CRL1206- FW-8R20ELF]	8.2 Ohm [PWR263S-20- 8R20F]		8.2 uH [SDR0703- 8R2ML]
8.2 Ohm [CRL1206- JW-8R20ELF]			8.2 uH [SDR0906- 8R2ML]
8.2 Ohm [CRL2010- FW-8R20ELF]			8.2 uH [SDR1006- 8R2ML]
8.2 Ohm [CRL2010- JW-8R20ELF]			

Multisim 14.1 Base Edition Components

8.2 uH [SDR1307-8R2ML]	8.2 uH [SRP5015TA-8R2M]	8.2 uH [SRR4028-8R2Y]	8.25 kOhm [CR0805-FX-8251ELF]
8.2 uH [SDR1307A-8R2M]	8.2 uH [SRP6540-8R2M]	8.2 uH [SRR5028-8R2Y]	8.25 kOhm [CR1206-FX-8251ELF]
8.2 uH [SDR1806-8R2ML]	8.2 uH [SRP7028A-8R2M]	8.2 uH [SRR6038-8R2Y]	8.25 kOhm [CRM0805-FX-8251ELF]
8.2 uH [SDR6603-8R2M]	8.2 uH [SRP7030-8R2FM]	8.2 uH [SRR6040A-8R2Y]	8.25 kOhm [CRT0603-DW-8251ELF]
8.2 uH [SRN5040-8R2M]	8.2 uH [SRP7050TA-8R2M]	8.2 uH [SRU1028-8R2Y]	8.25 kOhm [CRT0805-CX-8251ELF]
8.2 uH [SRN6045-8R2Y]	8.2 uH [SRR0805-8R2M]	8.2 uH [SRU1028A-8R2Y]	8.25 Ohm [CRM1206-FX-8R25ELF]
8.2 uH [SRN8040-8R2Y]	8.2 uH [SRR0906-8R2ML]	8.2 uH [SRU1038-8R2Y]	8.45 kOhm [CR0402-FX-8451GLF]
8.2 uH [SRP1038A-8R2M]	8.2 uH [SRR1210-8R2Y]	8.2 uH [SRU1048-8R2Y]	8.45 kOhm [CR0603-FX-8451ELF]
8.2 uH [SRP1040-8R2M]	8.2 uH [SRR1210A-8R2Y]	8.2 uH [SRU1048A-8R2Y]	8.45 kOhm [CR0805-FX-8451ELF]
8.2 uH [SRP1235-8R2M]	8.2 uH [SRR1240-8R2M]	8.2 uH [SRU6025-8R2Y]	8.45 kOhm [CR1206-FX-8451ELF]
8.2 uH [SRP1265A-8R2M]	8.2 uH [SRR1260-8R2Y]	8.2 uH [SRU6025A-8R2Y]	8.25 kOhm [CAY16-8251F4LF]
8.2 uH [SRP1270-8R2M]	8.2 uH [SRR1260A-8R2Y]	8.2 uH [SRU8028-8R2Y]	8.25 kOhm [CR0402-FX-8251GLF]
8.2 uH [SRP1770TA-8R2M]	8.2 uH [SRR1280-8R2Y]	8.25 kOhm [CAY16-8251F4LF]	8.25 kOhm [CR0603-FX-8251ELF]
8.2 uH [SRP4012TA-8R2M]	8.2 uH [SRR4011-8R2YL]	8.25 kOhm [CR0402-FX-8251GLF]	8.45 kOhm [CRT0603-BW-8451ELF]
8.2 uH [SRP4020TA-8R2M]	8.2 uH [SRR4018-8R2Y]	8.25 kOhm [CR0603-FX-8251ELF]	

Multisim 14.1 Base Edition Components

8.6 uH [SRR6028-8R6Y]	8.87 kOhm [CRT0603-CW-8871ELF]	80.6 Ohm [CR0603-FX-80R6ELF]	806 Ohm [CR0402-FX-8060GLF]
8.66 kOhm [CR0402-FX-8661GLF]	8.9 uH [SRR5018-8R9Y]	80.6 Ohm [CR0805-FX-80R6ELF]	806 Ohm [CR0603-FX-8060ELF]
8.66 kOhm [CR0603-FX-8661ELF]	80 kOhm [4309R-101-803]	80.6 Ohm [CR1206-FX-80R6ELF]	806 Ohm [CR0805-FX-8060ELF]
8.66 kOhm [CR0805-FX-8661ELF]	80 mOhm [CRA2512-FZ-R080ELF]	80.6 Ohm [CRT0402-BY-80R6GLF]	806 Ohm [CR1206-FX-8060ELF]
8.66 kOhm [CR1206-FX-8661ELF]	80 mOhm [CRA2512-JZ-R080ELF]	80.6 Ohm [CRT0805-BY-80R6ELF]	806 Ohm [CRT0603-DY-8060ELF]
8.66 kOhm [CRT0603-DX-8661ELF]	80 mOhm [PWR4412-2SCR0800F]	80.6 Ohm [PWR5322W80R6F E]	806 Ohm [CRT1206-BY-8060ELF]
8.7 uH [SRR6038-8R7Y]	80 mOhm [PWR4412-2SCR0800J]	800 nH [SRP1040-R80M]	80C186EA13
8.87 kOhm [CR0402-FX-8871GLF]	80.6 kOhm [CR0402-FX-8062GLF]	800 nH [SRP1045-R80M]	80C186EA20
8.87 kOhm [CR0603-FX-8871ELF]	80.6 kOhm [CR0603-FX-8062ELF]	800 nH [SRU1048-R80Y]	80C186EA25
8.87 kOhm [CR0603-FX-8871GLF]	80.6 kOhm [CR0805-FX-8062ELF]	806 kOhm [CR0402-FX-8063GLF]	80C186EB13
8.87 kOhm [CR0805-FX-8871ELF]	80.6 kOhm [CR1206-FX-8062ELF]	806 kOhm [CR0603-FX-8063ELF]	80C186EB20
8.87 kOhm [CR1206-FX-8871ELF]	80.6 Ohm [CR0402-FX-80R6GLF]	806 kOhm [CR0805-FX-8063ELF]	80C186EB25
			80C188EA13
			80C188EA20
			80C188EA25
			80C188EB13
			80C188EB20
			80C188EB25
			80L186EA13
			80L186EB13

Multisim 14.1 Base Edition Components

80L186EB16	82 kOhm [4308H-102-823]	82 kOhm [4420P-T01-823]	82 kOhm [4816P-1-823LF]
80L188EA13			
80L188EB13	82 kOhm [4308H-102-823LF]	82 kOhm [4420P-T02-823]	82 kOhm [4816P-2-823]
80L188EB16			
80SQ045NG	82 kOhm [4308R-101-823]	82 kOhm [4604X-102-823LF]	82 kOhm [4816P-2-823LF]
80SQ045NRLG	82 kOhm [4308R-101-823LF]	82 kOhm [4605X-101-823LF]	82 kOhm [4816P-T01-823]
82 kOhm [4114R-1-823]	82 kOhm [4308R-102-823]	82 kOhm [4606X-101-823LF]	82 kOhm [4816P-T01-823LF]
82 kOhm [4114R-1-823LF]	82 kOhm [4308R-102-823LF]	82 kOhm [4606X-102-823LF]	82 kOhm [4816P-T02-823]
82 kOhm [4114R-2-823]	82 kOhm [4310R-101-823]	82 kOhm [4608H-102-823LF]	82 kOhm [4816P-T02-823LF]
82 kOhm [4116R-1-823]	82 kOhm [4310R-101-823LF]	82 kOhm [4608X-101-823LF]	82 kOhm [CAT16-823J4LF]
82 kOhm [4116R-1-823LF]	82 kOhm [4310R-102-823]	82 kOhm [4608X-102-823LF]	82 kOhm [CAT25-823JALF]
82 kOhm [4116R-2-823]	82 kOhm [4310R-102-823LF]	82 kOhm [4609X-101-823LF]	82 kOhm [CAY16-8202F4LF]
82 kOhm [4116R-2-823LF]	82 kOhm [4416P-1-823]	82 kOhm [4610X-101-823LF]	82 kOhm [CAY16-823J4LF]
82 kOhm [4306M-102-823LF]	82 kOhm [4416P-T01-823]	82 kOhm [4610X-102-823LF]	82 kOhm [CAY16-823J8LF]
82 kOhm [4306R-101-823]	82 kOhm [4420P-1-823]	82 kOhm [4611X-101-823LF]	82 kOhm [CR0201-FW-8202GLF]
82 kOhm [4306R-101-823LF]	82 kOhm [4420P-1-823LF]	82 kOhm [4614X-102-823LF]	82 kOhm [CR0402-FX-8202GLF]
82 kOhm [4306R-102-823]	82 kOhm [4420P-2-823]	82 kOhm [4816P-1-823]	82 kOhm [CR0402-JW-823GLF]
82 kOhm [4306R-102-823LF]			

Multisim 14.1 Base Edition Components

82 kOhm [CR0603-FX-8202ELF]	82 mF [C0805C829K5GACT U]	82 nF [C0603C823K4RACT U]	82 nF [C0805F823K5RACT U]
82 kOhm [CR0603-JW-823ELF]	82 mF [C0805C829KBGACT U]	82 nF [C0603C823K5RACT U]	82 nF [C1206C823K1RACT U]
82 kOhm [CR0805-FX-8202ELF]	82 mOhm [CRL1206-JW-R082ELF]	82 nF [C0603C823K8RACT U]	82 nF [C1206C823K2RACT U]
82 kOhm [CR0805-JW-823ELF]	82 mOhm [CRM1206-FX-R082ELF]	82 nF [C0805C823K1RACT U]	82 nF [C1206C823K3HACT U]
82 kOhm [CR1206-FX-8202ELF]	82 mOhm [CRM2010-FX-R082ELF]	82 nF [C0805C823K3RACT U]	82 nF [C1206C823K3RACT U]
82 kOhm [CR1206-JW-823GLF]	82 mOhm [PWR4525NR082JE]	82 nF [C0805C823K4RACT U]	82 nF [C1206C823K5HACT U]
82 kOhm [CRM2512-JW-823ELF]	82 mOhm [PWR4525WR082JE]	82 nF [C0805C823K5RACT U]	82 nF [C1206C823K5RACT U]
82 kOhm [PWR263S-20-8202F]	82 nF [C0402C823K4RACT U]	82 nF [C0805C823K8RACT U]	82 nF [C1206C823KARACT U]
82 kOhm [PWR263S-20-8202FE]	82 nF [C0402C823K8RACT U]	82 nF [C0805C823M5UACT U]	82 nF [C1206C823M5UACT U]
82 kOhm [PWR263S-20-8202J]	82 nF [C0402C823K9RACT U]	82 nF [C0805F823K3RACT U]	82 nF [C1206F823K1RACT U]
82 mF [C0603C829K2GACT U]	82 nF [C0603C823K3RACT U]	82 nF [C0805F823K4RACT U]	82 nF [C1206F823K3RACT U]

Multisim 14.1 Base Edition Components

82 nF [C1206F823K4RACT U]	82 nF [C1210F823K2RACT U]	82 nF [GMC7.3823K63K31 TR12]	82 nF [MDC15823K630B5 3P3TUBE]
82 nF [C1206F823K5RACT U]	82 nF [C1812C823K1GACT U]	82 nF [MDC10823K100A5 2P3TUBE]	82 nF [MDK10823K630A5 8P7TUBE]
82 nF [C1210C823K1GACT U]	82 nF [C1812C823K1HACT U]	82 nF [MDC10823K250A5 2P3TUBE]	82 nF [MDK10823K630A5 8P8TUBE]
82 nF [C1210C823K1HACT U]	82 nF [C1812C823K5GACT U]	82 nF [MDC10823K400A5 2P3TUBE]	82 nF [MDK15823K400B5 3P3TUBE]
82 nF [C1210C823K1RACT U]	82 nF [C1812C823K5HACT U]	82 nF [MDC10823K50A52 P3TUBE]	82 nF [MDK15823K50B53 P3TUBE]
82 nF [C1210C823K3HACT U]	82 nF [C1812C823K5RACT U]	82 nF [MDC10823K630A5 8P7TUBE]	82 nF [MDS15823K400B5 3P3TUBE]
82 nF [C1210C823K5GACT U]	82 nF [C2220C823K1GACT U]	82 nF [MDC10823K630A5 8P8TUBE]	82 nF [MDS15823K50B53 P3TUBE]
82 nF [C1210C823K5HACT U]	82 nF [C2220C823K2GACT U]	82 nF [MDC15823K100B5 3P3TUBE]	82 nF [MDS15823K630B5 3P3TUBE]
82 nF [C1210C823K5RACT U]	82 nF [C2220C823K5GACT U]	82 nF [MDC15823K250B5 3P3TUBE]	82 Ohm [4114R-1- 820]
82 nF [C1210C823KARACT U]	82 nF [GMC5.7823K50J31 TR12]	82 nF [MDC15823K400B5 3P3TUBE]	82 Ohm [4114R-1- 820LF]
82 nF [C1210C823M1UAC TU]	82 nF [GMC7.3822K250K3 1TR12]	82 nF [MDC15823K50B53 P3TUBE]	82 Ohm [4114R-2- 820]
			82 Ohm [4116R-1- 820]

Multisim 14.1 Base Edition Components

82 Ohm [4116R-1-820LF]	82 Ohm [4310H-101-820LF]	82 Ohm [4605X-101-820LF]	82 Ohm [4816P-1-820]
82 Ohm [4116R-2-820]	82 Ohm [4310R-101-820]	82 Ohm [4606X-101-820LF]	82 Ohm [4816P-1-820LF]
82 Ohm [4116R-2-820LF]	82 Ohm [4310R-101-820LF]	82 Ohm [4606X-102-820LF]	82 Ohm [4816P-2-820]
82 Ohm [4306M-102-820]	82 Ohm [4310R-102-820]	82 Ohm [4607X-101-820LF]	82 Ohm [4816P-2-820LF]
82 Ohm [4306M-102-820LF]	82 Ohm [4310R-102-820LF]	82 Ohm [4608H-101-820LF]	82 Ohm [4816P-T01-820]
82 Ohm [4306R-101-820]	82 Ohm [4416P-1-820]	82 Ohm [4608X-101-820LF]	82 Ohm [4816P-T01-820LF]
82 Ohm [4306R-101-820LF]	82 Ohm [4416P-2-820]	82 Ohm [4608X-102-820LF]	82 Ohm [4816P-T02-820]
82 Ohm [4306R-102-820]	82 Ohm [4416P-T01-820]	82 Ohm [4609X-101-820LF]	82 Ohm [4816P-T02-820LF]
82 Ohm [4308H-101-820]	82 Ohm [4416P-T02-820]	82 Ohm [4610H-101-820LF]	82 Ohm [4818P-2-820]
82 Ohm [4308R-101-820]	82 Ohm [4420P-1-820]	82 Ohm [4610X-101-820LF]	82 Ohm [4820P-T01-820]
82 Ohm [4308R-101-820LF]	82 Ohm [4420P-2-820]	82 Ohm [4610X-102-820LF]	82 Ohm [CAT10-820J4LF]
82 Ohm [4308R-102-820]	82 Ohm [4420P-T01-820]	82 Ohm [4814P-2-820]	82 Ohm [CAT16-820J4LF]
82 Ohm [4308R-102-820LF]	82 Ohm [4420P-T02-820]	82 Ohm [4814P-2-820LF]	82 Ohm [CAT16-82R0F4LF]
82 Ohm [4309R-101-820]	82 Ohm [4604X-101-820LF]	82 Ohm [4814P-T02-820]	82 Ohm [CAT25-820J4LF]
82 Ohm [4310H-101-820]	82 Ohm [4604X-102-820LF]	82 Ohm [4814P-T02-820LF]	82 Ohm [CAY10-820J4LF]

Multisim 14.1 Base Edition Components

82 Ohm [CAY16-820J4LF]	82 Ohm [CR2512-JW-820ELF]	82 pF [C0402C820K5GACTU]	82 pF [C1206C820KCGACTU]
82 Ohm [CAY16-820J8LF]	82 Ohm [CRM1206-JW-820ELF]	82 pF [C0603C820K5GACTU]	82 pF [C1210C820KBGACTU]
82 Ohm [CAY16-82R0F4LF]	82 Ohm [CRM2512-JW-820ELF]	82 pF [C0805C820K1GACTU]	82 pF [C1812C820KBGACTU]
82 Ohm [CR0201-JW-820GLF]	82 Ohm [FW10A82R0JA]	82 pF [C0805C820K2GACTU]	82 pF [C1825C820KBGACTU]
82 Ohm [CR0402-FX-82R0GLF]	82 Ohm [FW20A82R0JA]	82 pF [C0805C820K3GACTU]	82 pF [C2220C820KBGACTU]
82 Ohm [CR0402-JW-820GLF]	82 Ohm [FW30A82R0JA]	82 pF [C0805C820K5GACTU]	82 pF [C2225C820KBGACTU]
82 Ohm [CR0603-FX-82R0ELF]	82 Ohm [FW50A82R0JA]	82 pF [C0805C820KBGACTU]	82 pF [CA064C820K2GACTU]
82 Ohm [CR0603-JW-820ELF]	82 Ohm [FW70A82R0JA]	82 pF [C1206C820K1GACTU]	82 pF [CDR31BP820BKSM]
82 Ohm [CR0805-FX-82R0ELF]	82 Ohm [PWR220T-20-82R0F]	82 pF [C1206C820K5GACTU]	82 pF [A700V826M004AT E018]
82 Ohm [CR0805-JW-820ELF]	82 Ohm [PWR263S-35-82R0FE]	82 pF [C1206C820K2GACTU]	82 pF [A700V826M004AT E025]
82 Ohm [CR1206-FX-82R0ELF]	82 Ohm [PWR4318W82R0JE]	82 pF [C1206C820KBGACTU]	82 pF [A700V826M004AT E028]
82 Ohm [CR1206-JW-820ELF]	82 pF [C0201C820K3GACTU]		
82 Ohm [CR2010-JW-820ELF]	82 pF [C0402C820K3GACTU]		

Multisim 14.1 Base Edition Components

82 uF [A700V826M006AT E018]	82 uH [SDR0302- 820KL]	82 uH [SRR0804- 820K]	82 uH [SRR4011- 820YL]
82 uF [A700V826M006AT E025]	82 uH [SDR0403- 820KL]	82 uH [SRR0805- 820K]	82 uH [SRR4018- 820Y]
82 uF [A700V826M006AT E028]	82 uH [SDR0503- 820KL]	82 uH [SRR0905- 820Y]	82 uH [SRR4028- 820Y]
82 uF [A700V826M006AT E018]	82 uH [SDR0603- 820KL]	82 uH [SRR0906- 820ML]	82 uH [SRR5018- 820Y]
82 uF [A700V826M2R5AT E018]	82 uH [SDR0604- 820KL]	82 uH [SRR0908- 820ML]	82 uH [SRR5028- 820Y]
82 uF [A700V826M2R5AT E025]	82 uH [SDR0703- 820KL]	82 uH [SRR1003- 820M]	82 uH [SRR6028- 820Y]
82 uF [A700V826M2R5AT E025]	82 uH [SDR0805- 820KL]	82 uH [SRR1005- 820Y]	82 uH [SRR6038- 820Y]
82 uF [A700V826M2R5AT E028]	82 uH [SDR0906- 820KL]	82 uH [SRR1206- 820YL]	82 uH [SRR6040A- 820M]
82 uF [EEFSX0G820ER]	82 uH [SDR1006- 820KL]	82 uH [SRR1208- 820YL]	82 uH [SRR7045- 820M]
82 uF [T520C826M008AT E025]	82 uH [SDR1105- 820KL]	82 uH [SRR1210- 820M]	82 uH [SRU1028- 820Y]
82 uF [T520C826M008AT E045]	82 uH [SDR1307- 820KL]	82 uH [SRR1210A- 820M]	82 uH [SRU1028A- 820Y]
82 uH [SDE0604A- 820K]	82 uH [SDR1307A- 820K]	82 uH [SRR1240- 820M]	82 uH [SRU1048- 820Y]
82 uH [SDE0805A- 820K]	82 uH [SDR6603- 820M]	82 uH [SRR1260- 820M]	82 uH [SRU1048A- 820Y]
82 uH [SDE1006A- 820K]	82 uH [SRR0735A- 820M]	82 uH [SRR1260A- 820M]	82.5 kOhm [CR0402-FX- 8252GLF]
	82 uH [SRR0745A- 820M]	82 uH [SRR1280- 820M]	82.5 kOhm [CR0603-FX- 8252ELF]

Multisim 14.1 Base Edition Components

82.5 kOhm [CR0805-FX- 8252ELF]	82.5 Ohm [CRT0402-FZ- 82R5GLF]	820 kOhm [4608X- AP2-824LF]	820 kOhm [CR0603-FX- 8203ELF]
82.5 kOhm [CR1206-FX- 8252ELF]	82.5 Ohm [CRT0805-CX- 82R5ELF]	820 kOhm [4609X- 101-824LF]	820 kOhm [CR0603-JW- 824ELF]
82.5 kOhm [CRT0402-BY- 8252GLF]	820 kOhm [4114R- 1-824]	820 kOhm [4610X- 102-824LF]	820 kOhm [CR0805-FX- 8203ELF]
82.5 kOhm [CRT0402-FZ- 8252GLF]	820 kOhm [4114R- 1-824LF]	820 kOhm [4816P- 1-824]	820 kOhm [CR0805-JW- 824ELF]
82.5 kOhm [CRT0603-BY- 8252ELF]	820 kOhm [4116R- 1-824]	820 kOhm [4816P- 1-824LF]	820 kOhm [CR1206-FX- 8203ELF]
82.5 kOhm [CRT1206-FZ- 8252ELF]	820 kOhm [4116R- 1-824LF]	820 kOhm [4816P- T01-824]	820 kOhm [CR1206-JW- 824ELF]
82.5 kOhm [CRT1206-FZ- 8252ELF]	820 kOhm [4306R- 102-824]	820 kOhm [4816P- T01-824LF]	820 kOhm [CR1206-JW- 824ELF]
82.5 Ohm [CAY16- 82R5F4LF]	820 kOhm [4308R- 102-824]	820 kOhm [4816P- T02-824]	820 kOhm [CR2010-JW- 824ELF]
82.5 Ohm [CR0402- FX-82R5GLF]	820 kOhm [4308R- 102-824LF]	820 kOhm [4816P- T02-824LF]	820 kOhm [CRM2010-FX- 8203ELF]
82.5 Ohm [CR0603- FX-82R5ELF]	820 kOhm [4310R- 102-824]	820 kOhm [CAT16- 824J4LF]	820 kOhm [CRM2010-FX- 8203ELF]
82.5 Ohm [CR0805- FX-82R5ELF]	820 kOhm [4605X- 101-824LF]	820 kOhm [CAT25- 824JALF]	820 mOhm [CR1206-J/-R82ELF]
82.5 Ohm [CR1206- FX-82R5ELF]	820 kOhm [4606X- 101-824LF]	820 kOhm [CAT25- 824JALF]	820 mOhm [CR1206-J/-R82ELF]
82.5 Ohm [CR2512- FX-82R5ELF]	820 kOhm [4606X- 102-824LF]	820 kOhm [CAY16- 824J4LF]	820 mOhm [CRL0603-FW- R820ELF]
82.5 Ohm [CRM1206-FX- 82R5ELF]	820 kOhm [4606X- 102-824LF]	820 kOhm [CAY16- 824J8LF]	820 mOhm [CRL0603-FW- R820ELF]
	820 kOhm [4608X- 101-824LF]	820 kOhm [CAY16- 824J8LF]	820 mOhm [CRL0603-JW- R820ELF]
	820 kOhm [4608X- 102-824LF]	820 kOhm [CR0402-FX- 8203GLF]	

Multisim 14.1 Base Edition Components

820 mOhm [CRL0805-FW- R820ELF]	820 mOhm [CRM2512-JX- R820ELF]	820 nF [C1812C824K5RACT U]	820 nF [MDC10824K100A5 2P3TUBE]
820 mOhm [CRL0805-JW- R820ELF]	820 nF [C0603C824K8PACT U]	820 nF [C1812C824M5UAC TU]	820 nF [MDC10824K250A5 7P7TUBE]
820 mOhm [CRL1206-FW- R820ELF]	820 nF [C0805C824K4RACT U]	820 nF [C1812F824K1RACT U]	820 nF [MDC10824K250A5 7P8TUBE]
820 mOhm [CRL1206-JW- R820ELF]	820 nF [C0805C824K8RACT U]	820 nF [C1812F824K3RACT U]	820 nF [MDC10824K50A52 P3TUBE]
820 mOhm [CRL2010-FW- R820ELF]	820 nF [C1206C824K3RACT U]	820 nF [C1812F824K5RACT U]	820 nF [MDC15824K100B5 3P3TUBE]
820 mOhm [CRL2010-JW- R820ELF]	820 nF [C1206C824K4RACT U]	820 nF [C1825C824KARACT U]	820 nF [MDC15824K50B53 P3TUBE]
820 mOhm [CRL2512-FW- R820ELF]	820 nF [C1206F824K4RACT U]	820 nF [C2220C824K1RACT U]	820 nF [MDK15824K100B5 3P3TUBE]
820 mOhm [CRL2512-JW- R820ELF]	820 nF [C1210C824K5RACT U]	820 nF [C2220C824K5RACT U]	820 nF [MDK15824K50B53 P3TUBE]
820 mOhm [CRM1206-FX- R820ELF]	820 nF [C1210C824K8RACT U]	820 nF [C2220C824KARACT U]	820 nF [MMC10.2824K63A 31TR16]
820 mOhm [CRM2010-FX- R820ELF]	820 nF [C1210F824K3RACT U]	820 nF [C2225C824K5RACT U]	820 nH [SRN4018- R82Y]
820 mOhm [CRM2512-FX- R820ELF]	820 nF [C1210F824K4RACT U]	820 nF [C2225C824KARACT U]	820 nH [SRP1235- R82M]
			820 nH [SRP1250- R82M]

Multisim 14.1 Base Edition Components

820 nH [SRP1265A-R82M]	820 Ohm [4306R-101-821LF]	820 Ohm [4310R-102-821LF]	820 Ohm [4609H-101-821LF]
820 nH [SRP6540-R82M]	820 Ohm [4306R-102-821]	820 Ohm [4311R-101-821]	820 Ohm [4609X-101-821LF]
820 nH [SRP7028A-R82M]	820 Ohm [4306R-102-821LF]	820 Ohm [4420P-2-821]	820 Ohm [4610X-101-821LF]
820 nH [SRP7030-R82FM]	820 Ohm [4308M-101-821]	820 Ohm [4420P-T02-821]	820 Ohm [4610X-102-821LF]
820 nH [SRP7050TA-R82M]	820 Ohm [4308M-102-821]	820 Ohm [4604X-101-821LF]	820 Ohm [4610X-AP1-821LF]
820 Ohm [4114R-1-821]	820 Ohm [4308M-102-821LF]	820 Ohm [4605M-101-821LF]	820 Ohm [4611X-101-821LF]
820 Ohm [4114R-1-821LF]	820 Ohm [4308R-101-821]	820 Ohm [4605X-101-821LF]	820 Ohm [4612X-101-821LF]
820 Ohm [4114R-2-821]	820 Ohm [4308R-101-821LF]	820 Ohm [4606X-101-821LF]	820 Ohm [4612X-102-821LF]
820 Ohm [4116R-1-821]	820 Ohm [4308R-102-821]	820 Ohm [4606X-102-821LF]	820 Ohm [4814P-2-821]
820 Ohm [4116R-1-821LF]	820 Ohm [4308R-102-821LF]	820 Ohm [4607X-101-821LF]	820 Ohm [4814P-T02-821]
820 Ohm [4116R-2-821]	820 Ohm [4309R-101-821]	820 Ohm [4608H-101-821LF]	820 Ohm [4816P-1-821]
820 Ohm [4116R-2-821LF]	820 Ohm [4309R-101-821LF]	820 Ohm [4608M-102-821LF]	820 Ohm [4816P-1-821LF]
820 Ohm [4306H-101-821]	820 Ohm [4310R-101-821]	820 Ohm [4608X-101-821LF]	820 Ohm [4816P-2-821]
820 Ohm [4306H-101-821LF]	820 Ohm [4310R-101-821LF]	820 Ohm [4608X-102-821LF]	820 Ohm [4816P-2-821LF]
820 Ohm [4306R-101-821]	820 Ohm [4310R-102-821]	820 Ohm [4608X-AP1-821LF]	820 Ohm [4816P-T01-821]

Multisim 14.1 Base Edition Components

820 Ohm [4816P-T01-821LF]	820 Ohm [CR0805-FX-8200GLF]	820 pF [C0402C821K3HACT U]	820 pF [C0603C821K3RACT U]
820 Ohm [4816P-T02-821]	820 Ohm [CR0805-JW-821ELF]	820 pF [C0402C821K3RACT U]	820 pF [C0603C821K4RACT U]
820 Ohm [4816P-T02-821LF]	820 Ohm [CR0805-JW-821GLF]	820 pF [C0402C821K4RACT U]	820 pF [C0603C821K5GACT U]
820 Ohm [CAT16-8200F4LF]	820 Ohm [CR1206-FX-8200ELF]	820 pF [C0402C821K5HACT U]	820 pF [C0603C821K5HACT U]
820 Ohm [CAT16-821J4LF]	820 Ohm [CR2010-JW-821ELF]	820 pF [C0402C821K5RACT U]	820 pF [C0603C821K5RACT U]
820 Ohm [CAT25-821JALF]	820 Ohm [CR2512-FX-8200ELF]	820 pF [C0402C821K8RACT U]	820 pF [C0805C821K1RACT U]
820 Ohm [CAY10-821J4LF]	820 Ohm [CRM1206-FX-8200ELF]	820 pF [C0603C821K1HACT U]	820 pF [C0805C821K2RACT U]
820 Ohm [CAY16-821J4LF]	820 Ohm [PWR163S-25-8200F]	820 pF [C0603C821K1RACT U]	820 pF [C0805C821K4GACT U]
820 Ohm [CAY16-821J8LF]	820 Ohm [PWR163S-25-8200JE]	820 pF [C0603C821K2RACT U]	820 pF [C0805C821K5GACT U]
820 Ohm [CR0402-FX-8200GLF]	820 pF [C0402C821K1HACT U]	820 pF [C0603C821K3GACT U]	820 pF [C0805C821K5RACT U]
820 Ohm [CR0402-JW-821GLF]	820 pF [C0402C821K3GACT U]	820 pF [C0603C821K3HACT U]	
820 Ohm [CR0603-FX-8200ELF]			
820 Ohm [CR0603-JW-821ELF]			
820 Ohm [CR0603-JW-821GLF]			
820 Ohm [CR0805-FX-8200ELF]			

Multisim 14.1 Base Edition Components

820 pF [C1206C821K1GACT U]	820 uF [2SEPC820MD]	820 uH [SDR6603- 821M]	820 uH [SRR7045- 821M]
820 pF [C1206C821K2GACT U]	820 uF [2SEPC820MW]	820 uH [SRR0745A- 821M]	825 kOhm [CR0402-FX- 8253GLF]
820 pF [C1206C821K5GACT U]	820 uF [2SEPC820MX]	820 uH [SRR0805- 821K]	825 kOhm [CR0603-FX- 8253ELF]
820 pF [C1210C821KBGAC TU]	820 uH [SDE1006A- 821K]	820 uH [SRR0908- 821YL]	825 kOhm [CR0805-FX- 8253ELF]
820 pF [C1812C821K2GACT U]	820 uH [SDR0302- 821KL]	820 uH [SRR1005- 821K]	825 kOhm [CR1206-FX- 8253ELF]
820 pF [C1812C821K5GACT U]	820 uH [SDR0403- 821KL]	820 uH [SRR1205- 821KL]	825 kOhm [CRT1206-BW- 8253ELF]
820 pF [C1812C821KBGAC TU]	820 uH [SDR0503- 821KL]	820 uH [SRR1206- 821KL]	825 Ohm [CAY16- 8250F4LF]
820 pF [C1812C821KBGAC TU]	820 uH [SDR0604- 821KL]	820 uH [SRR1208- 821KL]	825 Ohm [CR0402- FX-8250GLF]
820 pF [C1825C821KBGAC TU]	820 uH [SDR0703- 821KL]	820 uH [SRR1210- 821M]	825 Ohm [CR0603- FX-8250ELF]
820 pF [C2220C821KBGAC TU]	820 uH [SDR0805- 821KL]	820 uH [SRR1210A- 821M]	825 Ohm [CR0805- FX-8250ELF]
820 pF [C2225C821KBGAC TU]	820 uH [SDR0906- 821KL]	820 uH [SRR1240- 821K]	825 Ohm [CR1206- FX-8250ELF]
820 pF [CDR32BP821BKSM]	820 uH [SDR1006- 821KL]	820 uH [SRR1260- 821K]	825 Ohm [CRM1206-FX- 8250ELF]
	820 uH [SDR1307- 821KL]	820 uH [SRR1260A- 821K]	825 Ohm [CRT0402-FZ- 8250GLF]
	820 uH [SDR1307A- 821K]	820 uH [SRR1280- 821K]	

Multisim 14.1 Base Edition Components

825 Ohm [CRT0805-BY- 8250ELF]	845 kOhm [CR0603-FX- 8453ELF]	86.6 kOhm [CR0201-FW- 8662GLF]	866 kOhm [CR0402-FX- 8663GLF]
825 Ohm [CRT0805-CX- 8250ELF]	845 kOhm [CR0805-FX- 8453ELF]	86.6 kOhm [CR0402-FX- 8662GLF]	866 kOhm [CR0805-FX- 8663ELF]
825 Ohm [PWR2615W8250FE]	845 kOhm [CR1206-FX- 8453ELF]	86.6 kOhm [CR0603-FX- 8662ELF]	866 kOhm [CR1206-FX- 8663ELF]
84.5 kOhm [CR0402-FX- 8452GLF]	845 Ohm [CR0402- FX-8450GLF]	86.6 kOhm [CR0805-FX- 8662ELF]	866 Ohm [CR0402- FX-8660GLF]
84.5 kOhm [CR0603-FX- 8452ELF]	845 Ohm [CR0603- FX-8450ELF]	86.6 kOhm [CR1206-FX- 8662ELF]	866 Ohm [CR0603- FX-8660ELF]
84.5 kOhm [CR0805-FX- 8452ELF]	845 Ohm [CR0805- FX-8450ELF]	86.6 kOhm [CR1206-FX- 8662ELF]	866 Ohm [CR0805- FX-8660ELF]
84.5 kOhm [CR0805-FX- 8452ELF]	845 Ohm [CR1206- FX-8450ELF]	86.6 kOhm [CRT0805-FX- 8662ELF]	866 Ohm [CR1206- FX-8660ELF]
84.5 kOhm [CR1206-FX- 8452ELF]	845 Ohm [CRT0805-BY- 8450ELF]	86.6 kOhm [CRT1206-BW- 8662ELF]	866 Ohm [CRT0402-BY- 8660GLF]
84.5 Ohm [CAY16- 84R5F4LF]	85 mOhm [CRA2512-JZ- R085ELF]	86.6 Ohm [CAT16- 86R6F4LF]	87520-0010BLF
84.5 Ohm [CR0603- FX-84R5ELF]	850 nH [SRP1205- R60Y]	86.6 Ohm [CAY16- 86R6F4LF]	88.7 kOhm [CR0402-FX- 8872GLF]
84.5 Ohm [CR0805- FX-84R5ELF]	850 Ohm [PWR220T-35- 8500J]	86.6 Ohm [CR0402- FX-86R6GLF]	88.7 kOhm [CR0603-FX- 8872ELF]
84.5 Ohm [CR1206- FX-84R5ELF]	8550-4500PL	86.6 Ohm [CR0603- FX-86R6ELF]	88.7 kOhm [CR0805-FX- 8872ELF]
845 kOhm [CR0402-FX- 8453GLF]	86 kOhm [4116R-1- 863LF]	86.6 Ohm [CR0805- FX-86R6ELF]	88.7 kOhm [CR1206-FX- 8872ELF]
		86.6 Ohm [CR1206- FX-86R6ELF]	

Multisim 14.1 Base Edition Components

88.7 Ohm [CR0603-FX-88R7ELF]	8Line_Isolated	9.1 kOhm [4304M-101-912]	9.1 MOhm [CR0805-JW-915ELF]
88.7 Ohm [CR0805-FX-88R7ELF]	8POS_ROTARY	9.1 kOhm [4306M-101-912]	9.1 MOhm [CR1206-JW-915ELF]
88.7 Ohm [CR1206-FX-88R7ELF]	9 mOhm [CRE2512-FZ-R009E-2]	9.1 kOhm [4306M-101-912LF]	9.1 nF [C0603C912K3HACT U]
88.7 Ohm [CRM2512-FX-88R7ELF]	9 mOhm [CRE2512-FZ-R009E-3]	9.1 kOhm [CAY16-912J4LF]	9.1 nF [C0805C912K1GACT U]
880 nH [SRP4020-R88M]	9 uH [SRP1250-9R0M]	9.1 kOhm [CR0402-FX-9101GLF]	9.1 nF [C0805C912K1HACT U]
887 kOhm [CR0402-FX-8873GLF]	9 uH [SRR5018-9R0Y]	9.1 kOhm [CR0603-FX-9101ELF]	9.1 nF [C0805C912K3HACT U]
887 kOhm [CR0603-FX-8873ELF]	9.09 kOhm [CR0402-FX-9091GLF]	9.1 kOhm [CR0603-JW-912ELF]	9.1 nF [C0805C912K5GACT U]
887 kOhm [CR0805-FX-8873ELF]	9.09 kOhm [CR0603-FX-9091ELF]	9.1 kOhm [CR0805-FX-9101ELF]	9.1 nF [C0805C912K5HACT U]
887 kOhm [CR1206-FX-8873ELF]	9.09 kOhm [CR0805-FX-9091ELF]	9.1 kOhm [CR1206-FX-9101ELF]	9.1 nF [C1206C912K1HACT U]
887 Ohm [CR0402-FX-8870GLF]	9.09 kOhm [CR1206-FX-9091ELF]	9.1 kOhm [CR2512-JW-912ELF]	9.1 nF [C1206C912K3GACT U]
887 Ohm [CR0603-FX-8870ELF]	9.09 kOhm [CRT0603-BY-9091ELF]	9.1 MOhm [CHV0603-FX-9104ELF]	9.1 nF [C1206C912K3HACT U]
887 Ohm [CR0805-FX-8870ELF]	9.09 kOhm [CRT0603-FY-9091ELF]	9.1 MOhm [CR0603-JW-915ELF]	
887 Ohm [CR1206-FX-8870ELF]	9.09 Ohm [PWR6327W9R09F]		
8Line_Bussed			

Multisim 14.1 Base Edition Components

9.1 nF [C1206C912K5HACT U]	9.1 Ohm [CRM2512-JW- 9R1ELF]	9.53 kOhm [CR0603-FX- 9531ELF]	90 mOhm [CRM0805-FW- R090ELF]
9.1 nF [CDR35BP912BKSM]	9.1 Ohm [CRT0603- BY-9R10ELF] 9.1 Ohm [CRT0805- BW-9R10ELF]	9.53 kOhm [CR0805-FX- 9531ELF]	90 mOhm [CRM2010-FX- R090ELF]
9.1 Ohm [CR0402- J/-9R1GLF]	9.1 Ohm [FW10A9R10JA]	9.53 kOhm [CR1206-FX- 9531ELF]	90.9 kOhm [CR0201-FW- 9092GLF]
9.1 Ohm [CR0603- J/-9R1ELF]	9.1 Ohm [FW20A9R10JA]	9.53 kOhm [CRT0805-BW- 9531ELF]	90.9 kOhm [CR0402-FX- 9092GLF]
9.1 Ohm [CR0805- J/-9R1ELF]	9.1 Ohm [FW70A9R10JA]	9.6 kOhm [4116R- 1-962]	90.9 kOhm [CR0603-FX- 9092ELF]
9.1 Ohm [CR1206- J/-9R1ELF]	9.31 kOhm [CR0402-FX- 9311GLF]	9.6 kOhm [4116R- 1-962LF]	90.9 kOhm [CR0603-FX- 9092GLF]
9.1 Ohm [CRL0603- FW-9R10ELF]	9.31 kOhm [CR0603-FX- 9311ELF]	9.76 kOhm [CR0402-FX- 9761GLF]	90.9 kOhm [CR0805-FX- 9092ELF]
9.1 Ohm [CRL0805- FW-9R10ELF]	9.31 kOhm [CR0805-FX- 9311ELF]	9.76 kOhm [CR0603-FX- 9761ELF]	90.9 kOhm [CR1206-FX- 9092ELF]
9.1 Ohm [CRL1206- FW-9R10ELF]	9.31 kOhm [CRL1206- JW-9R10ELF]	9.76 kOhm [CR0805-FX- 9761ELF]	90.9 kOhm [CRM0805-FX- 9092ELF]
9.1 Ohm [CRL1206- JW-9R10ELF]	9.31 kOhm [CRL2010- FW-9R10ELF]	9.76 kOhm [CR1206-FX- 9761ELF]	90.9 Ohm [CR0402- FX-90R9GLF]
9.1 Ohm [CRL2010- FW-9R10ELF]	9.31 kOhm [CRL2512- FW-9R10ELF]	9.76 kOhm [CRT0805-BV- 9761ELF]	90.9 Ohm [CR0603- FX-90R9ELF]
9.1 Ohm [CRL2512- FW-9R10ELF]	9.53 kOhm [CR0402-FX- 9531GLF]	9.76 kOhm [CRT0805-BY- 9761ELF]	90.9 Ohm [CR0805- FX-90R9ELF]
9.1 Ohm [CRM1206-FX- 9R10ELF]			

Multisim 14.1 Base Edition Components

90.9 Ohm [CR1206-FX-90R9ELF]	909 Ohm [CR1206-FX-9090ELF]	91 kOhm [CR0805-JW-913ELF]	91 Ohm [CR0402-JW-910GLF]
90.9 Ohm [CR2512-FX-90R9ELF]	909 Ohm [CR2512-FX-9090ELF]	91 kOhm [CR1206-FX-9102ELF]	91 Ohm [CR0603-FX-91R0ELF]
90.9 Ohm [CRT0805-BY-90R9ELF]	909 Ohm [CRT0402-FZ-9090GLF]	91 kOhm [CR1206-JW-913ELF]	91 Ohm [CR0603-JW-910ELF]
900 nH [SRN6028-R90Y]	91 kOhm [4114R-1-913]	91 kOhm [CRT0603-BZ-9102ELF]	91 Ohm [CR0805-FX-91R0ELF]
900 nH [SRP1206-R60Y]	91 kOhm [4114R-1-913LF]	91 mF [C0805C919KBGAC TU]	91 Ohm [CR0805-JW-910ELF]
900 nH [SRR1305-R90ZL]	91 kOhm [4116R-1-913]	91 Ohm [4306M-102-910]	91 Ohm [CR1206-FX-91R0ELF]
909 kOhm [CR0402-FX-9093GLF]	91 kOhm [4116R-1-913LF]	91 Ohm [4308M-102-910]	91 Ohm [CR1206-JW-910ELF]
909 kOhm [CR0603-FX-9093ELF]	91 kOhm [CAT16-913J4LF]	91 Ohm [4308M-102-910LF]	91 Ohm [CR2512-JW-910ELF]
909 kOhm [CR0805-FX-9093ELF]	91 kOhm [CAY16-913J4LF]	91 Ohm [4608X-102-910LF]	91 Ohm [CRM2512-JW-910ELF]
909 kOhm [CR0402-FX-9093ELF]	91 kOhm [CR0201-FW-9102GLF]	91 Ohm [4820P-1-910]	91 pF [C0805C910K2GACT U]
909 kOhm [CR1206-FX-9093ELF]	91 kOhm [CR0402-FX-9102GLF]	91 Ohm [4820P-T02-910]	91 pF [C0805C910KBGAC TU]
909 Ohm [CR0402-FX-9090GLF]	91 kOhm [CR0402-JW-913GLF]	91 Ohm [CAT10-910J4LF]	91 pF [C1206C910K1GACT U]
909 Ohm [CR0603-FX-9090ELF]	91 kOhm [CR0603-FX-9102ELF]	91 Ohm [CAY16-910J4LF]	91 pF [C1206C910KBGAC TU]
909 Ohm [CR0805-FX-9090ELF]	91 kOhm [CR0603-JW-913ELF]	91 Ohm [CAY16-91R0F4LF]	
	91 kOhm [CR0805-FX-9102ELF]	91 Ohm [CR0402-FX-91R0GLF]	

Multisim 14.1 Base Edition Components

91 pF [C1210C910KBGAC TU]	910 kOhm [CR0805-FX- 9103ELF]	910 mOhm [CRL2010-FW- R910ELF]	910 Ohm [4310H- 101-911]
91 pF [C1812C910KBGAC TU]	910 kOhm [CR0805-JW- 914ELF]	910 mOhm [CRL2010-JW- R910ELF]	910 Ohm [4310M- 101-911]
91 pF [C1825C910KBGAC TU]	910 kOhm [CR1206-FX- 9103ELF]	910 mOhm [CRL2512-FW- R910ELF]	910 Ohm [CAY10- 911J4LF]
91 pF [C2220C910KBGAC TU]	910 kOhm [CR1206-JW- 914ELF]	910 mOhm [CRL2512-JW- R910ELF]	910 Ohm [CR0402- FX-9100GLF]
91 pF [C2225C910KBGAC TU]	910 kOhm [CRT0805-BY- 9103ELF]	910 mOhm [CRM0805-FX- R910ELF]	910 Ohm [CR0402- JW-911GLF]
910 kOhm [CAY16- 914J4LF]	910 mOhm [CRL0603-FW- R910ELF]	910 mOhm [CRM1206-FX- R910ELF]	910 Ohm [CR0603- JW-911ELF]
910 kOhm [CHV0603-FX- 9103ELF]	910 mOhm [CRL0603-JW- R910ELF]	910 mOhm [CRM2010-FX- R910ELF]	910 Ohm [CR0805- FX-9100ELF]
910 kOhm [CR0402-FX- 9103GLF]	910 mOhm [CRL0805-FW- R910ELF]	910 mOhm [CRM2512-FX- R910ELF]	910 Ohm [CR0805- JW-911ELF]
910 kOhm [CR0402-JW- 914GLF]	910 mOhm [CRL0805-JW- R910ELF]	910 mOhm [CRM2512-JX- R910ELF]	910 Ohm [CR1206- JW-911ELF]
910 kOhm [CR0603-FX- 9103ELF]	910 mOhm [CRL1206-FW- R910ELF]	910 Ohm [4116R-1- 911]	910 Ohm [CR2010- JW-911ELF]
910 kOhm [CR0603-JW- 914ELF]	910 mOhm [CRL1206-JW- R910ELF]	910 Ohm [4308H- 101-911]	910 Ohm [CR2512- JW-911ELF]
		910 Ohm [4308R- 101-911]	910 Ohm [CRT1206-AV- 9100ELF]

Multisim 14.1 Base Edition Components

910 Ohm [CRT1206-BY- 9100ELF]	910 pF [C1825C911KBGAC TU]	931 kOhm [CR0402-FX- 9313GLF]	95 Ohm [4308H- 101-950]
910 pF [C0402C911K1HACT U]	910 pF [C2220C911KBGAC TU]	931 kOhm [CR0603-FX- 9313ELF]	95 Ohm [4308H- 101-950LF]
910 pF [C0402C911K3HACT U]	910 pF [C2225C911KBGAC TU]	931 kOhm [CR0805-FX- 9313ELF]	95 Ohm [4310H- 102-950]
910 pF [C0402C911K5HACT U]	93.1 kOhm [CR0402-FX- 9312GLF]	931 kOhm [CR1206-FX- 9313ELF]	95 Ohm [4816P-1- 950]
910 pF [C0603C911K1HACT U]	93.1 kOhm [CR0603-FX- 9312ELF]	931 Ohm [CR0402- FX-9310GLF]	95 Ohm [4816P-2- 950]
910 pF [C0603C911K3HACT U]	93.1 kOhm [CR0805-FX- 9312ELF]	931 Ohm [CR0603- FX-9310ELF]	95 Ohm [4816P-2- 950LF]
910 pF [C0603C911K5GACT U]	93.1 kOhm [CR1206-FX- 9312ELF]	931 Ohm [CR0805- FX-9310ELF]	95.3 kOhm [CR0201-FW- 9532GLF]
910 pF [C0603C911K5HACT U]	93.1 Ohm [CR0402- FX-93R1GLF]	931 Ohm [CR1206- FX-9310ELF]	95.3 kOhm [CR0402-FX- 9532GLF]
910 pF [C0805C911K5GACT U]	93.1 Ohm [CR0603- FX-93R1ELF]	931 Ohm [CRM2512-FX- 9310ELF]	95.3 kOhm [CR0603-FX- 9532ELF]
910 pF [C1210C911KBGAC TU]	93.1 Ohm [CR0805- FX-93R1ELF]	931 Ohm [CRT0603-BY- 9310ELF]	95.3 kOhm [CR0805-FX- 9532ELF]
910 pF [C1812C911KBGAC TU]	93.1 Ohm [CR1206- FX-93R1ELF]	95 mOhm [CRA2512-JZ- R095ELF]	95.3 kOhm [CR1206-FX- 9532ELF]
	93.1 Ohm [CR2010- FX-93R1ELF]	95 Ohm [4114R-2- 950LF]	95.3 kOhm [CRT0603-BY- 9532ELF]
		95 Ohm [4306R- 101-950]	

Multisim 14.1 Base Edition Components

95.3 kOhm [CRT0805-BW- 9532ELF]	953 Ohm [CR1206- FX-9530ELF]	976 kOhm [CR0402-FX- 9763GLF]	AC_VOLTAGE
95.3 Ohm [CR0402- FX-95R3GLF]	953 Ohm [CRT1206-BY- 9530ELF]	976 kOhm [CR0603-FX- 9763ELF]	ACML-7400-000E
95.3 Ohm [CR0603- FX-95R3ELF]	97.6 kOhm [CR0402-FX- 9762GLF]	976 kOhm [CR0805-FX- 9763ELF]	ACML-7410-000E
95.3 Ohm [CR0805- FX-95R3ELF]	97.6 kOhm [CR0603-FX- 9762ELF]	976 kOhm [CR1206-FX- 9763ELF]	ACML-7420-000E
95.3 Ohm [CR1206- FX-95R3ELF]	97.6 kOhm [CR0805-FX- 9762ELF]	976 Ohm [CR0402- FX-9760GLF]	ACNT-H313-000E
95.3 Ohm [CRT0402-FZ- 95R3GLF]	97.6 kOhm [CR1206-FX- 9762ELF]	976 Ohm [CR0603- FX-9760ELF]	ACNW261L-000E
953 kOhm [CR0402-FX- 9533GLF]	97.6 kOhm [CRT0603-BY- 9762ELF]	976 Ohm [CR0805- FX-9760ELF]	ACNW261L-300E
953 kOhm [CR0603-FX- 9533ELF]	97.6 kOhm [CRT0805-BY- 9762ELF]	976 Ohm [CR1206- FX-9760ELF]	ACNW3410-000E
953 kOhm [CR0805-FX- 9533ELF]	97.6 Ohm [CR0402- FX-97R6GLF]	976 Ohm [CRT0603-BY- 9760ELF]	ACNW3410-300E
953 kOhm [CR1206-FX- 9533ELF]	97.6 Ohm [CR0603- FX-97R6ELF]	9Line_Bussed	ACNW3430-000E
953 Ohm [CR0402- FX-9530GLF]	97.6 Ohm [CR0805- FX-97R6ELF]	9Line_Isolated	ACNW3430-300E
953 Ohm [CR0603- FX-9530ELF]	97.6 Ohm [CR1206- FX-97R6ELF]	ABM_CURRENT	ACPL-021L-000E
953 Ohm [CR0805- FX-9530ELF]		ABM_VOLTAGE	ACPL-021L-060E
		AC_CURRENT	ACPL-024L-000E
		AC_POWER	ACPL-024L-060E
			ACPL-054L-000E
			ACPL-054L-060E
			ACPL-061L-000E
			ACPL-061L-060E
			ACPL-064L-000E
			ACPL-064L-060E
			ACPL-077L-000E
			ACPL-077L-060E
			ACPL-214-500E
			ACPL-214-50AE

Multisim 14.1 Base Edition Components

ACPL-214-560E	ACPL-798J-000E	ACPL-K64L-060E	ACPL-P341-000E
ACPL-214-56AE	ACPL-C61L-000E	ACPL-M21L-000E	ACPL-P341-060E
ACPL-217-500E	ACPL-C61L-060E	ACPL-M21L-060E	ACPL-P343-000E
ACPL-217-50AE	ACPL-C790-000E	ACPL-M43T-000E	ACPL-P343-060E
ACPL-217-50BE	ACPL-C797-000E	ACPL-M43T-060E	ACPL-P345-000E
ACPL-217-50CE	ACPL-C799-000E	ACPL-M46T-000E	ACPL-P345-060E
ACPL-217-50DE	ACPL-C79A-000E	ACPL-M46T-060E	ACPL-P346-000E
ACPL-217-560E	ACPL-C79B-000E	ACPL-M483-000E	ACPL-P346-060E
ACPL-217-56AE	ACPL-C87AT-000E	ACPL-M483-060E	ACPL-P347-000E
ACPL-217-56BE	ACPL-C87BT-000E	ACPL-M484-000E	ACPL-P347-060E
ACPL-217-56CE	ACPL-H342-000E	ACPL-M484-060E	ACPL-P349-000E
ACPL-217-56DE	ACPL-H342-060E	ACPL-M49T-000E	ACPL-P349-060E
ACPL-312U-000E	ACPL-K30T-000E	ACPL-M49T-060E	ACPL-P483-000E
ACPL-312U-300E	ACPL-K30T-060E	ACPL-M50L-000E	ACPL-P483-060E
ACPL-32JT-000E	ACPL-K342-000E	ACPL-M50L-060E	ACPL-P484-000E
ACPL-331J-000E	ACPL-K342-060E	ACPL-M61L-000E	ACPL-P484-060E
ACPL-332J-000E	ACPL-K34T-000E	ACPL-M61L-060E	ACPL-W340-000E
ACPL-336J-000E	ACPL-K34T-060E	ACPL-M61T-000E	ACPL-W340-060E
ACPL-337J-000E	ACPL-K43T-000E	ACPL-M61T-060E	ACPL-W341-000E
ACPL-339J-000E	ACPL-K43T-060E	ACPL-M71T-000E	ACPL-W341-060E
ACPL-34JT-000E	ACPL-K44T-000E	ACPL-M71T-060E	ACPL-W343-000E
ACPL-782T-000E	ACPL-K44T-060E	ACPL-M72T-000E	ACPL-W343-060E
ACPL-782T-300E	ACPL-K54L-000E	ACPL-M72T-060E	ACPL-W345-000E
ACPL-796J-000E	ACPL-K54L-060E	ACPL-P340-000E	ACPL-W345-060E
ACPL-796J-060E	ACPL-K64L-000E	ACPL-P340-060E	ACPL-W346-000E

Multisim 14.1 Base Edition Components

ACPL-W346-060E	AD22050R	AD536AJH	AD548BQ
ACPL-W347-000E	AD22057N	AD536AJQ	AD548BR
ACPL-W347-060E	AD22057R	AD536ASE/883B	AD548CH
ACPL-W349-000E	AD380JH	AD542JH	AD548CQ
ACPL-W349-060E	AD380KH	AD542KH	AD548JN
ACPL-W483-000E	AD380LH	AD542LH	AD548JR
ACPL-W483-060E	AD380SH	AD542SH	AD548KN
ACPL-W484-000E	AD507JH	AD544JH	AD548SH
ACPL-W484-060E	AD507KH	AD544KH	AD548SQ
ACPL-W50L-000E	AD507SH	AD544LH	AD548TH
ACPL-W50L-060E	AD509JH	AD544SH	AD548TQ
ACPL-W61L-000E	AD509KH	AD545AJH	AD549JH
ACPL-W61L-060E	AD509SH	AD545AKH	AD549JHZ
ACSL-6400-00TE	AD515AJH	AD545ALH	AD549KH
ACSL-6400-06TE	AD515AKH	AD545AMH	AD549KHZ
ACSL-7210-00RE	AD515ALH	AD546JN	AD549LH
ACSL-7210-06RE	AD517JH	AD546KN	AD549LHZ
ACTEL-FLASHPRO- HDR	AD517KH	AD547JH	AD549SH
	AD517LH	AD547KH	AD549SH/883B
AD1580ART	AD517SH	AD547LH	AD5530_SO16
AD1580ARTZ	AD5260_SO14	AD547SH	AD5531_SO16
AD1580BKSZ	AD5262_SO16	AD548AH	AD5539JN
AD1580BRT	AD5280_SO14	AD548AQ	AD5539JQ
AD1580BRTZ	AD5282_SO16	AD548AR	AD5539SQ
AD22050N	AD536AJD	AD548BH	AD5539SQ/883B

Multisim 14.1 Base Edition Components

AD581JH	AD588BD	AD623AN	AD630JN
AD581KH	AD588BQ	AD623AR	AD630KN
AD581LH	AD588JQ	AD623ARM	AD630SD
AD581SH	AD588KQ	AD623BN	AD630SE/883B
AD581TH	AD588SD	AD623BR	AD633AN
AD581UH	AD588TD	AD624AD	AD633ANZ
AD584JH	AD588TQ/883B	AD624BD	AD633AR
AD584JN	AD600AQ	AD624CD	AD633ARZ
AD584KH	AD600AR	AD624SD	AD633JN
AD584KN	AD600JN	AD626AN	AD633JR
AD584LH	AD602AQ	AD626AR	AD636JD
AD584SH	AD602AR	AD626BN	AD636JH
AD584TH	AD602JN	AD627AN	AD636KD
AD587JN	AD603AQ	AD627AR	AD636KH
AD587JNZ	AD603AR	AD627BN	AD637AQ
AD587JQ	AD604AN	AD627BR	AD637AR
AD587JR	AD604AR	AD628ARMZ	AD637ARZ
AD587JRZ	AD604ARS	AD628ARZ	AD637BR
AD587KN	AD605AN	AD629AN	AD637BRZ
AD587KR	AD605AR	AD629AR	AD637JD
AD587KRZ	AD620AN	AD629BN	AD637JDZ
AD587UQ	AD620AR	AD629BR	AD637JQ
AD588AD	AD620BN	AD630AD	AD637JRZ
AD588AQ	AD620BR	AD630AR	AD637JRZ-R7
AD588ARWZ	AD620SQ	AD630BD	AD637JRZ-RL

Multisim 14.1 Base Edition Components

AD637KDZ	AD680AN	AD706KN	AD711JR
AD637KQ	AD680AR	AD706TQ	AD711KN
AD637KRZ	AD680JR	AD707AH	AD711KR
AD637SD	AD680JTZ	AD707AQ	AD711SH
AD637SD/883B	AD704AN	AD707AR	AD711SQ
AD637SQ/883B	AD704AQ	AD707JN	AD711TH
AD642JH	AD704AR	AD707KN	AD711TQ
AD642KH	AD704BQ	AD707KR	AD712AH
AD642LH	AD704JN	AD707TH	AD712AQ
AD642SH	AD704JR	AD707TQ	AD712BH
AD644JH	AD704JR-16	AD708AH	AD712BQ
AD644KH	AD704KN	AD708AQ	AD712CH
AD644LH	AD704TQ	AD708BH	AD712CQ
AD644SH	AD704TQ/883B	AD708BQ	AD712JN
AD645AH	AD705AQ	AD708JN	AD712JR
AD645BH	AD705BQ	AD708SH	AD712KN
AD645JN	AD705JN	AD708SH/883B	AD712KR
AD645KN	AD705JR	AD708SQ	AD712SH
AD645SH	AD705KN	AD711AH	AD712SQ
AD647JH	AD705TQ	AD711AQ	AD712SQ/883B
AD647KH	AD706AQ	AD711BH	AD712TH
AD647LH	AD706AR	AD711BQ	AD712TQ
AD647SE	AD706BQ	AD711CH	AD712TRZ-EP
AD647SEB	AD706JN	AD711CQ	AD713AQ
AD647SH	AD706JR	AD711JN	AD713BQ

Multisim 14.1 Base Edition Components

AD713JN	AD741KH	AD744SH	AD795JR
AD713JR	AD741KN	AD744SQ	AD795JRZ
AD713JR-16	AD741LH	AD744TH	AD795KN
AD713KN	AD741LN	AD744TH/883B	AD796AN
AD713SQ	AD741SH	AD744TQ	AD796AR
AD713SQ/883B	AD743AN	AD745AN	AD796BN
AD713TQ	AD743AQ	AD745AQ	AD796SQ/883B
AD713TQ/883B	AD743AR	AD745AR	AD797AN
AD734AN	AD743BQ	AD745BQ	AD797AR
AD734AQ	AD743JN	AD745JN	AD797BN
AD734BN	AD743JR	AD745JR	AD797SQ
AD734BQ	AD743KN	AD745KN	AD8000YCPZ
AD734SQ	AD743KR	AD745SQ	AD8000YCPZ-REEL
AD734SQ/883B	AD743SQ	AD745SQ/883B	AD8000YRDZ
AD736AQ	AD743SQ/883B	AD746AQ	AD8001AN
AD736AR	AD744AH	AD746BQ	AD8001AQ
AD736JNZ	AD744AQ	AD746JN	AD8001AR
AD737AN	AD744BH	AD746JR	AD8001ART
AD737AR	AD744BQ	AD746SQ	AD8002AN
AD737BQ	AD744CH	AD780AN	AD8002AR
AD741CH	AD744CQ	AD780AR	AD8002ARM
AD741CN	AD744JN	AD780BN	AD8003ACPZ
AD741H	AD744JR	AD780BR	AD8003ACPZ-R2
AD741JH	AD744KN	AD795BH	AD8004AN
AD741JN	AD744KR	AD795JN	AD8004AR

Multisim 14.1 Base Edition Components

AD8004AR-14	AD8016ARP	AD8029AKS	AD8032BNZ
AD8004SQ	AD8017AR	AD8029AKSZ-R2	AD8032BR
AD8005AN	AD8018AR	AD8029AR	AD8032BRZ
AD8005AR	AD8018ARU	AD8029ARZ	AD8033AKS
AD8005ART	AD8021AR	AD8030AR	AD8033AR
AD8007AKS	AD8021ARM	AD8030ARJ	AD8034AR
AD8007AR	AD8021ARMZ	AD8030ARJZ-R2	AD8034ART
AD8008AR	AD8021ARZ	AD8030ARZ	AD8034ARTZ-R2
AD8008ARM	AD8022AR	AD8031AN	AD8034ARZ
AD8009AR	AD8022ARM	AD8031ANZ	AD8036AN
AD8009ARZ	AD8022ARMZ	AD8031AR	AD8036AR
AD8009JRT	AD8022ARZ	AD8031ART	AD8038AKS
AD8010AN	AD8023AR	AD8031ARTZ	AD8038AKSZ-R2
AD8010AR	AD8024AR	AD8031ARZ	AD8038AR
AD8010AR-16	AD8027AR	AD8031BN	AD8038ARZ
AD8011AN	AD8027ART	AD8031BNZ	AD8039AR
AD8011AR	AD8027ARTZ	AD8031BR	AD8039ART
AD8012AR	AD8027ARTZ-R2	AD8031BRZ	AD8039ARTZ-R2
AD8012ARM	AD8027ARTZ-REEL	AD8032AN	AD8039ARZ
AD8012ARMZ	AD8027ARTZ-REEL7	AD8032ANZ	AD8040AR
AD8014AR	AD8027ARZ	AD8032AR	AD8040ARU
AD8014ART	AD8027ARZ-REEL	AD8032ARM	AD8040ARUZ
AD8016ARB	AD8027ARZ-REEL7	AD8032ARMZ	AD8040ARZ
AD8016ARE	AD8028ARMZ	AD8032ARZ	AD8041AN
AD8016AREZ	AD8028ARZ	AD8032BN	AD8041AR

Multisim 14.1 Base Edition Components

AD8042AN	AD8057AR	AD8079BR	AD8129ARZ-REEL7
AD8042AR	AD8057ART	AD8091AR	AD812AN
AD8044AN	AD8057ARTZ-R2	AD8091ART	AD812AR
AD8044AR	AD8057ARZ	AD8092AR	AD8130AR
AD8045ACP	AD8058AR	AD8092ARM	AD8130ARM
AD8045ACPZ-R2	AD8058ARM	AD8099ACP	AD8131AR
AD8045ARD	AD8061AR	AD8099ACPZ-R2	AD8131ARM
AD8045ARDZ	AD8061ART	AD8099ARD	AD8131ARMZ
AD8047AN	AD8062AR	AD8099ARDZ	AD8131ARZ
AD8047AR	AD8062ARM	AD810AN	AD8132AR
AD8048AN	AD8062ARMZ	AD810AR	AD8132ARM
AD8048AR	AD8062ARZ	AD810SN	AD8132ARMZ
AD8051AR	AD8065AR	AD810SR	AD8132ARZ
AD8051ART	AD8065ART	AD811AN	AD8133ACP-R2
AD8052AR	AD8065ARTZ	AD811AR-16	AD8137YCP
AD8052ARM	AD8065ARZ	AD811AR-20	AD8137YCPZ
AD8054AR	AD8066AR	AD811JR	AD8137YR
AD8054ARU	AD8066ARM	AD811SE/883B	AD8137YRZ
AD8055AN	AD8066ARMZ	AD811SQ/883B	AD8138AR
AD8055AR	AD8066ARZ	AD8129ARMZ	AD8138ARM
AD8055ART	AD8067ART	AD8129ARMZ-REEL	AD8138ARMZ
AD8055ARZ	AD8067ARTZ-R2	AD8129ARMZ-REEL7	AD8138ARZ
AD8056AN	AD8072ARM	AD8129ARZ	AD8139ACP
AD8056AR	AD8072JR	AD8129ARZ-REEL	AD8139ACPZ
AD8056ARM	AD8079AR		AD8139ACPZ-R2

Multisim 14.1 Base Edition Components

AD8139ARD	AD8206WYRZ-RL	AD8217BRMZ-R7	AD8222HACPZ-R7
AD8139ARDZ	AD8206YRZ	AD8217BRMZ-RL	AD8222HBCPZ-R7
AD813AN	AD8206YRZ-REEL	AD8218BCPZ-RL	AD8224ACPZ-R7
AD813AR	AD8206YRZ-REEL7	AD8218BRMZ	AD8224ACPZ-RL
AD813AR-14	AD8207WBRZ	AD8218BRMZ-R7	AD8224ACPZ-WP
AD8145YCPZ-R2	AD8207WBRZ-R7	AD8219BRMZ	AD8224BCPZ-R7
AD8146ACPZ-R2	AD8207WBRZ-RL	AD8219BRMZ-RL	AD8224BCPZ-RL
AD8147ACPZ-R2	AD8208WBRMZ	AD8220ARMZ	AD8224BCPZ-WP
AD8148ACPZ-R2	AD8208WBRZ	AD8220ARMZ-R7	AD8224HACPZ-R7
AD815ARB-24	AD8209WBRMZ	AD8220ARMZ-RL	AD8224HACPZ-RL
AD817AN	AD820AN	AD8220BRMZ	AD8224HACPZ-WP
AD817AR	AD820AR	AD8220BRMZ-R7	AD8224HBCPZ-R7
AD8184AN	AD820BN	AD8220BRMZ-RL	AD8224HBCPZ-RL
AD818AN	AD820BR	AD8220WARMZ	AD8224HBCPZ-WP
AD818AR	AD8210WYRZ	AD8220WARMZ-R7	AD8225AR
AD8205WHRZ	AD8210YRZ	AD8220WARMZ-RL	AD8226ARMZ
AD8205WHRZ-RL	AD8211YRJZ-R2	AD8221AR	AD8226ARZ
AD8205WYRZ	AD8214ARMZ	AD8221ARM	AD8226BRMZ
AD8205WYRZ-R7	AD8216WYRZ	AD8221ARMZ	AD8226BRZ
AD8205WYRZ-RL	AD8216WYRZ-R7	AD8221ARZ	AD8227ARMZ
AD8205YRZ	AD8216WYRZ-RL	AD8221BR	AD8227ARZ
AD8205YRZ-R7	AD8216YRZ	AD8221BRZ	AD8227BRMZ
AD8205YRZ-RL	AD8216YRZ-R7	AD8221TRMZ-EP	AD8227BRZ
AD8206WYRZ	AD8216YRZ-RL	AD8222ACPZ-R7	AD8228ARMZ
AD8206WYRZ-R7	AD8217BRMZ	AD8222BCPZ-R7	AD8228ARZ

Multisim 14.1 Base Edition Components

AD8228BRMZ	AD8251ARMZ	AD8277BRZ	AD8330ACPZ-R2
AD8228BRZ	AD8253ARMZ	AD8278ARMZ	AD8330ACPZ-R7
AD8229HDZ	AD8253ARMZ-R7	AD8278ARZ	AD8330ACPZ-RL
AD822AN	AD8253ARMZ-RL	AD8278BRMZ	AD8330ARQZ
AD822AR	AD825AR	AD8278BRZ	AD8330ARQZ-R7
AD822ARM	AD825AR-16	AD8279ARZ	AD8330ARQZ-RL
AD822BN	AD826AN	AD8279BRZ	AD8331ARQZ
AD822BR	AD826AR	AD827AQ	AD8331ARQZ-R7
AD822SQ	AD8270ACPZ-R7	AD827JN	AD8331ARQZ-RL
AD8232ACPZ-R7	AD8273ARZ	AD827JR-16	AD8332ACPZ-R2
AD8235ACBZ-P7	AD8273ARZ-R7	AD827SE/883B	AD8332ACPZ-R7
AD8236ARMZ	AD8273ARZ-RL	AD827SQ	AD8332ACPZ-RL
AD8237ARMZ	AD8274ARMZ	AD827SQ/883B	AD8332ARU
AD8237ARMZ-R7	AD8274ARMZ-R7	AD828AN	AD8332ARU-REEL
AD8237ARMZ-RL	AD8274ARMZ-RL	AD828AR	AD8332ARU-REEL7
AD823AN	AD8274ARZ	AD829AQ	AD8332ARUZ
AD823ANZ	AD8274ARZ-R7	AD829JN	AD8332ARUZ-R7
AD823AR	AD8274ARZ-RL	AD829JR	AD8332ARUZ-RL
AD8244ARMZ	AD8275ARMZ	AD829SE/883B	AD8333ACPZ-REEL
AD8244BRMZ	AD8275BRMZ	AD829SQ	AD8333ACPZ-REEL7
AD824AN	AD8276ARMZ	AD829SQ/883B	AD8333ACPZ-WP
AD824AR-14	AD8276ARZ	AD8304ARU	AD8334ACPZ
AD824AR-16	AD8276BRMZ	AD830AN	AD8334ACPZ-REEL
AD824BN	AD8276BRZ	AD830JR	AD8334ACPZ-REEL7
AD8250ARMZ	AD8277ARZ	AD8310ARM	AD8335ACPZ

Multisim 14.1 Base Edition Components

AD8335ACPZ-REEL	AD840SQ-883B	AD8420ARMZ-RL	AD8422BRZ
AD8335ACPZ-REEL7	AD8417BRMZ	AD8421ARMZ	AD8422BRZ-R7
AD8336ACPZ-R7	AD8417WBRMZ	AD8421ARMZ-R7	AD8422BRZ-RL
AD8336ACPZ-RL	AD8417WBRZ	AD8421ARMZ-RL	AD8426ACPZ-R7
AD8336ACPZ-WP	AD8417WHRMZ	AD8421ARZ	AD8426ACPZ-WP
AD8337BCPZ-R2	AD8417WHRZ	AD8421ARZ-R7	AD8426BCPZ-R7
AD8337BCPZ-REEL	AD8418ABRMZ	AD8421ARZ-RL	AD8426BCPZ-WP
AD8337BCPZ-REEL7	AD8418AWBRMZ	AD8421BRMZ	AD8428ARZ
AD8337BCPZ-WP	AD8418AWBRZ	AD8421BRMZ-R7	AD8428BRZ
AD834AQ	AD8418AWHRMZ	AD8421BRMZ-RL	AD8429ARZ
AD834ARZ	AD8418AWHRZ	AD8421BRZ	AD8429ARZ-R7
AD834JNZ	AD8418BRMZ	AD8421BRZ-R7	AD8429BRZ
AD834JRZ	AD8418WBRMZ	AD8421BRZ-RL	AD8429BRZ-R7
AD834SQ/883B	AD8418WBRZ	AD8421TRMZ-EP	AD842JH
AD835ANZ	AD841JH	AD8421TRMZ-EP-R7	AD842JN
AD835AR	AD841JN	AD8422ARMZ	AD842JQ
AD835ARZ	AD841JQ	AD8422ARMZ-R7	AD842JR
AD8397ARDZ	AD841KH	AD8422ARMZ-RL	AD842KH
AD8397ARZ	AD841KN	AD8422ARZ	AD842KN
AD840JN	AD841KQ	AD8422ARZ-R7	AD842KQ
AD840JQ	AD841SE	AD8422ARZ-RL	AD842SE
AD840KN	AD841SH	AD8422BRMZ	AD842SH
AD840KQ	AD841SQ	AD8422BRMZ-R7	AD842SQ
AD840SE-883B	AD8420ARMZ	AD8422BRMZ-RL	AD8436ACPZ-R7
AD840SQ	AD8420ARMZ-R7		AD8436ACPZ-RL

Multisim 14.1 Base Edition Components

AD8436ACPZ-WP	AD844JRZ-16	AD8476ACPZ-R7	AD848SQ
AD8436ARQZ	AD844SQ	AD8476ACPZ-RL	AD848SQ/883B
AD8436ARQZ-R7	AD8450ASTZ	AD8476ACPZ-WP	AD8494ARMZ
AD8436ARQZ-RL	AD8451ASTZ	AD8476ARMZ	AD8494ARMZ-R7
AD8436BRQZ	AD845AQ	AD8476ARMZ-R7	AD8494CRMZ
AD8436BRQZ-R7	AD845BQ	AD8476ARMZ-RL	AD8494CRMZ-R7
AD8436BRQZ-RL	AD845JN	AD8476BCPZ-R7	AD8495ARMZ
AD8436JCPZ-R7	AD845JR	AD8476BCPZ-RL	AD8495ARMZ-R7
AD8436JCPZ-RL	AD845JR-16	AD8476BCPZ-WP	AD8495CRMZ
AD8436JCPZ-WP	AD845KN	AD8476BRMZ	AD8495CRMZ-R7
AD843AQ	AD845SQ	AD8476BRMZ-R7	AD8496ARMZ
AD843BH	AD845SQ/883B	AD8476BRMZ-RL	AD8496ARMZ-R7
AD843BQ	AD846AN	AD8479ARZ	AD8496CRMZ
AD843JN	AD846AQ	AD8479ARZ-RL	AD8496CRMZ-R7
AD843JR	AD846BQ	AD8479BRZ	AD8497ARMZ
AD843JR-16	AD846SQ	AD8479BRZ-RL	AD8497ARMZ-R7
AD843KN	AD8475ACPZ-R7	AD847AQ	AD8497CRMZ
AD843SE	AD8475ACPZ-RL	AD847AR	AD8497CRMZ-R7
AD843SE/883B	AD8475ACPZ-WP	AD847JN	AD849AQ
AD843SH	AD8475ARMZ	AD847JR	AD849JN
AD843SQ	AD8475ARMZ-R7	AD847SQ	AD849JR
AD843SQ/883B	AD8475ARMZ-RL	AD847SQ/883B	AD849SQ
AD844AN	AD8475BRMZ	AD848AQ	AD849SQ/883B
AD844AQ	AD8475BRMZ-R7	AD848JN	AD8500AKSZ
AD844BQ	AD8475BRMZ-RL	AD848JR	AD8500AKSZ-R2

Multisim 14.1 Base Edition Components

AD8502ARJZ	AD8531AKSZ-R2	AD8542ARU	AD8574ARU
AD8504ARUZ	AD8531AR	AD8544AR	AD8591ART
AD8505ACBZ-R7	AD8531ARTZ-REEL	AD8544ARU	AD8592ARM
AD8505ARJZ-RL	AD8531ARZ	AD8546ARMZ	AD8594AR
AD8506ARMZ	AD8532AR	AD8548ARZ	AD8594ARU
AD8508ACBZ-REEL	AD8532ARM	AD8548ARZ-R7	AD8597ACPZ-R2
AD8508ARUZ	AD8532ARMZ-R2	AD8548ARZ-RL	AD8597ARZ
AD8510AR	AD8532ARU	AD8551AR	AD8599ARZ
AD8510ARM	AD8532ARUZ	AD8551ARM	AD8601ART
AD8510BR	AD8532ARZ	AD8552AR	AD8602AR
AD8512AR	AD8534AR	AD8552ARU	AD8602ARM
AD8512ARM	AD8534ARU	AD8554AR	AD8603AUJZ
AD8512BR	AD8534ARUZ	AD8554ARU	AD8604AR
AD8513AR	AD8534ARZ	AD8561AN	AD8604ARQZ
AD8513ARU	AD8538ARZ	AD8561AR	AD8604ARUZ
AD8515AKS	AD8538AUJZ	AD8561ARU	AD8604DRU
AD8515ART	AD8538AUJZ-R2	AD8564AN	AD8604DRZ
AD8517ART	AD8539ARMZ	AD8564AR	AD8605ACB
AD8519AKS	AD8539ARZ	AD8565AKS	AD8605ACBZ-REEL7
AD8519AR	AD8541AKS	AD8565AKSZ	AD8605ART
AD8519ART	AD8541AR	AD8571AR	AD8605ARTZ-R2
AD8527AR	AD8541ART	AD8571ARM	AD8606ACBZ-REEL
AD8529AR	AD8541ARZ	AD8572AR	AD8606AR
AD8529ARM	AD8542AR	AD8572ARU	AD8606ARM-REEL
AD8531AKS	AD8542ARM	AD8574AR	AD8606ARMZ-REEL

Multisim 14.1 Base Edition Components

AD8606ARZ	AD8617WARMZ-REEL	AD8629ARZ	AD8644AR
AD8607AR		AD8629WARZ-RL	AD8644ARU
AD8607ARM-REEL	AD8617WARZ-RL	AD8630ARUZ	AD8646ARMZ
AD8608AR	AD8618AR	AD8630ARZ	AD8646ARZ
AD8608ARU	AD8618ARU	AD8630WARZ-RL	AD8646WARMZ-RL
AD8608ARUZ	AD8619ARUZ	AD8631ART	AD8646WARZ-RL
AD8608ARZ	AD8619ARZ	AD8631ARTZ	AD8648ARUZ
AD8609AR	AD8620AR	AD8632AR	AD8648ARZ
AD8609ARU	AD8620BR	AD8632ARM	AD8648WARUZ
AD8610AR	AD8622ARMZ	AD8632ARMZ	AD8651AR
AD8610ARM	AD8622ARZ	AD8632ARZ	AD8651ARM
AD8610ARZ	AD8624ACPZ-R2	AD8634HRZN	AD8655ARMZ
AD8610BR	AD8624ARUZ	AD8638ARJZ	AD8655ARZ
AD8611AR	AD8625ARUZ	AD8638ARZ	AD8656ARMZ
AD8611ARM	AD8625ARZ	AD8639ACPZ-R2	AD8656ARZ
AD8612ARU	AD8626ARMZ	AD8639ARMZ	AD8657ACPZ-RL
AD8613AKSZ	AD8626ARZ	AD8639ARZ	AD8657ARMZ
AD8613AUJZ	AD8627AKS	AD8639WARZ	AD8659ACPZ-R7
AD8614ART	AD8627AKSZ	AD8641AKSZ	AD8659ACPZ-RL
AD8615AUJZ	AD8627AR	AD8641AKSZ-R2	AD8659ARZ
AD8616AR	AD8627ARZ	AD8641ARZ	AD8659ARZ-R7
AD8616ARM	AD8628AR	AD8642ARMZ	AD8659ARZ-RL
AD8617ACPZ-R2	AD8628ART	AD8642ARZ	AD8661ACPZ-R2
AD8617ARMZ	AD8628AUJ	AD8643ACPZ-R2	AD8661ARZ
AD8617ARZ	AD8629ARMZ	AD8643ARZ	AD8662ARMZ

Multisim 14.1 Base Edition Components

AD8662ARZ	AD8676ARZ	AD9618JR	ADA4001-2ARZ
AD8663ACPZ	AD8676BRMZ	AD9618SQ	ADA4001-2ARZ-R7
AD8663ARZ	AD8676BRZ	AD9618TQ	ADA4001-2ARZ-RL
AD8664ARUZ	AD8677ARZ	AD9620AD	ADA4004-1ARJZ-R2
AD8664ARZ	AD8677AUJZ-R2	AD9620SD	ADA4004-1ARJZ-R7
AD8665ARJZ-R2	AD8691AKSZ	AD9621AN	ADA4004-1ARJZ-RL
AD8665ARZ	AD8691AUJZ	AD9622AN	ADA4004-1ARZ
AD8666ARMZ	AD8692ARMZ	AD9623AN	ADA4004-1ARZ-R7
AD8666ARZ	AD8692ARZ	AD9624AN	ADA4004-1ARZ-RL
AD8666WARZ-R7	AD8694ARUZ	AD9630AN	ADA4004-2ARMZ
AD8667ARMZ	AD8694ARZ	AD9630AQ	ADA4004-2ARMZ-R7
AD8667ARZ	AD8698AR	AD9630AR	ADA4004-2ARMZ-RL
AD8669ARUZ	AD8698ARM	AD9631AN	ADA4004-2ARZ
AD8669ARZ	AD9218_FP48	AD9631AR	ADA4004-2ARZ-R7
AD8671AR	AD9610TH	AD9632AN	ADA4004-2ARZ-RL
AD8671ARM	AD9610TH/883B	AD9632AR	ADA4004-4ACPZ-R2
AD8671ARMZ	AD9617AQ	AD9841A-LQFP(48)	ADA4004-4ACPZ-R7
AD8672AR	AD9617BQ	AD9842A-LQFP(48)	ADA4000-1ARZ
AD8672ARM	AD9617JN	ADA4000-1AUJZ	ADA4004-4ACPZ-RL
AD8672ARMZ	AD9617JR	ADA4000-1AUJZ-RL	ADA4004-4ARZ
AD8674AR	AD9617SQ	ADA4000-2ARMZ	ADA4004-4ARZ-R7
AD8674ARU	AD9617TQ	ADA4000-2ARZ	ADA4004-4ARZ-RL
AD8675ARMZ	AD9618AQ	ADA4000-4ARUZ	ADA4051-1AKSZ-R2
AD8675ARZ	AD9618BQ	ADA4000-4ARZ	ADA4051-1ARJZ-R2
AD8676ARMZ	AD9618JN		ADA4051-2ACPZ-R2

Multisim 14.1 Base Edition Components

ADA4051-2ARMZ	ADA4084-1ARZ	ADA4177-1ARZ	ADA4610-1ARJZ-R2
ADA4062-2ACPZ-RL	ADA4084-2ACPZ-R7	ADA4177-2ARMZ	ADA4610-1ARZ
ADA4062-2ARMZ	ADA4084-2ARMZ	ADA4177-2ARZ	ADA4610-1BRZ
ADA4062-2ARZ	ADA4084-2ARMZ-R7	ADA4177-4ARUZ	ADA4610-2ACPZ-R7
ADA4062-2BRZ	ADA4084-2ARMZ-RL	ADA4177-4ARZ	ADA4610-2ACPZ-RL
ADA4062-4ACPZ-R2	ADA4084-2ARMZ-RL	ADA4350ARUZ	ADA4610-2ARMZ
ADA4062-4ARUZ	ADA4084-2ARZ	ADA4433-1BCPZ-R2	ADA4610-2ARMZ-R7
ADA4075-2ACPZ-RL	ADA4084-2ARZ-R7	ADA4433-1WBCPZ-R7	ADA4610-2ARMZ-RL
ADA4075-2ARZ	ADA4084-2ARZ-RL	ADA4500-2ACPZ-R7	ADA4610-2ARZ
ADA4077-1ARMZ	ADA4084-4ACPZ-R7	ADA4500-2ACPZ-RL	ADA4610-2ARZ-R7
ADA4077-1ARZ	ADA4084-4ARUZ	ADA4500-2ARMZ	ADA4610-2ARZ-RL
ADA4077-1BRZ	ADA4091-2ACPZ-R2	ADA4500-2ARMZ-R7	ADA4610-2BRZ
ADA4077-2ARMZ	ADA4091-2ARZ	ADA4500-2ARMZ-RL	ADA4610-2BRZ-R7
ADA4077-2ARMZ-R7	ADA4091-4ACPZ-R2	ADA4505-1ACBZ-R7	ADA4610-2BRZ-RL
ADA4077-2ARMZ-RL	ADA4091-4ARUZ	ADA4505-1ARJZ-R2	ADA4610-4ACPZ-R7
ADA4077-2ARZ	ADA4092-4ARUZ	ADA4505-2ACBZ-RL	ADA4610-4ARZ
ADA4077-2ARZ-R7	ADA4096-2ACPZ-R7	ADA4505-2ARMZ	ADA4622-2ACPZ-R7
ADA4077-2ARZ-RL	ADA4096-2WARMZ-R7	ADA4505-4ACBZ-RL	ADA4622-2ARMZ
ADA4077-2BRZ	ADA4096-2WARMZ-RL	ADA4528-1ACPZ-R2	ADA4622-2ARZ
ADA4077-2BRZ-R7	ADA4096-4ACPZ-R7	ADA4528-1ARMZ	ADA4622-2BRZ
ADA4077-2BRZ-RL	ADA4096-4ARUZ	ADA4528-2ACPZ-R7	ADA4627-1ACPZ-RL
ADA4077-4ARUZ	ADA4177-1ARMZ	ADA4528-2ARMZ	ADA4627-1ARZ
ADA4077-4ARZ			ADA4627-1BRZ
ADA4084-1ARJZ-R2			ADA4637-1ACPZ-R2

Multisim 14.1 Base Edition Components

ADA4637-1ARZ	ADA4692-2ACPZ-R7	ADA4850-1YCPZ-R2	ADA4860-1YRJZ-RL
ADA4637-1BRZ	ADA4692-2ARZ	ADA4850-2YCPZ-R2	ADA4860-1YRJZ-RL7
ADA4638-1ACPZ-R7	ADA4692-4ARUZ	ADA4850-2YCPZ-RL	ADA4861-3YRZ
ADA4638-1ACPZ-RL	ADA4700-1ARDZ	ADA4851-1WYRJZ-R7	ADA4861-3YRZ-RL
ADA4638-1ARZ	ADA4805-1AKSZ-R2	ADA4851-1YRJZ-R2	ADA4861-3YRZ-RL7
ADA4638-1ARZ-R7	ADA4805-1ARJZ-R2	ADA4851-1YRJZ-RL	ADA4870ARRZ
ADA4638-1ARZ-RL	ADA4805-2ACPZ-R2	ADA4851-2WYRMZ	ADA4891-1ARJZ-R7
ADA4661-2ACPZ-R7	ADA4807-1AKSZ-R2	ADA4851-2YRMZ	ADA4891-1ARZ
ADA4661-2ACPZ-RL	ADA4807-1ARJZ-R2	ADA4851-2YRMZ-RL	ADA4891-2ARMZ
ADA4661-2ARMZ	ADA4807-2ACPZ-R2	ADA4851-4WYRUZ	ADA4891-2ARZ
ADA4661-2ARMZ-R7	ADA4817-1ACPZ-R2	ADA4851-4YRUZ	ADA4891-3ARUZ
ADA4661-2ARMZ-RL	ADA4817-1ACPZ-R7	ADA4851-4YRUZ-RL	ADA4891-3ARZ
ADA4665-2ARMZ	ADA4817-1ACPZ-RL	ADA4853-1AKSZ-R2	ADA4891-4ARUZ
ADA4665-2ARZ	ADA4817-1ARDZ	ADA4853-2YCPZ-R2	ADA4891-4ARZ
ADA4666-2ACPZ-R7	ADA4817-1ARDZ-R7	ADA4853-3WYCPZ-R7	ADA4895-1ARJZ-R2
ADA4666-2ACPZ-RL	ADA4817-2ACPZ-R2	ADA4853-3YCPZ-R2	ADA4895-1ARZ
ADA4666-2ARMZ	ADA4817-2ACPZ-R7	ADA4853-3YRUZ	ADA4895-2ARMZ
ADA4666-2ARMZ-R7	ADA4817-2ACPZ-RL	ADA4855-3YCPZ-R2	ADA4895-2ARMZ-R7
ADA4666-2ARMZ-RL	ADA4841-1YRJZ-R2	ADA4857-1YCPZ-R2	ADA4895-2ARMZ-RL
ADA4691-2ACBZ-R7	ADA4841-1YRZ	ADA4857-1YRZ	ADA4896-2ACPZ-R2
ADA4691-2ACPZ-R7	ADA4841-2YCPZ-R2	ADA4857-2YCPZ-R2	ADA4896-2ACPZ-R7
ADA4691-4ACPZ-R7	ADA4841-2YRMZ	ADA4858-3ACPZ-R2	ADA4896-2ACPZ-RL
	ADA4841-2YRZ	ADA4860-1YRJZ-R2	ADA4896-2ARMZ
	ADA4850-1YCPZ		

Multisim 14.1 Base Edition Components

ADA4896-2ARMZ-R7	ADA4938-1ACPZ-R2	ADG1213YCPZ-500RL7	ADG411BN
	ADA4938-2ACPZ-R2		ADG411BR
ADA4896-2ARMZ-RL	ADA4939-1YCPZ-R2	ADG1213YRUZ	ADG411BRU
ADA4897-1ARJZ-R2	ADA4939-2YCPZ-R2	ADG1236YCPZ-500RL7	ADG411TQ
ADA4897-1ARZ	ADA4940-1ACPZ-R2	ADG1236YRUZ	ADG412
ADA4897-1SRJZ-EPR7	ADA4940-1ACPZ-R7	ADG1311YRUZ	ADG412BN
	ADA4940-1ACPZ-RL	ADG1311YRZ	ADG412BR
ADA4897-2ARMZ	ADA4940-2ACPZ-R2	ADG1312YRUZ	ADG412BRU
ADA4897-2TRMZ-EP	ADA4940-2ACPZ-R7	ADG1312YRZ	ADG412TQ
	ADA4940-2ACPZ-RL	ADG1313YRUZ	ADG413BN
ADA4898-1YRDZ	ADA4941-1YCPZ-RL	ADG1313YRZ	ADG413BNZ
ADA4898-2YRDZ	ADA4941-1YRZ	ADG406BN	ADG413BR
ADA4899-1YCPZ	ADA4950-1YCPZ-R2	ADG406BP	ADG413BRUZ
ADA4899-1YCPZ-R2	ADA4950-2YCPZ-R2	ADG407BN	ADG426BN
ADA4899-1YRDZ	ADA4960-1ACPZ-R2	ADG407BP	ADG426BRS
ADA4922-1ACPZ-R2	ADC	ADG408	ADG441ABN
ADA4922-1ARDZ	ADC16	ADG408BN	ADG441ABR
ADA4927-1YCPZ-R2	ADD_FULL	ADG408BR	ADG441BN
ADA4927-2YCPZ	ADD_FULL4_FCR	ADG408BRU	ADG441BR
ADA4930-1YCPZ-R2	ADD_HALF	ADG408TQ	ADG441TQ
ADA4930-2YCPZ-R2	ADG1211YCPZ-500RL7	ADG409BN	ADG442BN
ADA4932-1YCPZ-R2	ADG1211YRUZ	ADG409BR	ADG444
ADA4932-2YCPZ-R2		ADG409BRU	ADG444ABN
ADA4937-1YCPZ-R2	ADG1212YCPZ-500RL7	ADG409TQ	ADG444ABR
ADA4937-2YCPZ-R2	ADG1212YRUZ	ADG411	ADG444BN

Multisim 14.1 Base Edition Components

ADG444BR	ADG528FTQ	ADG659YCPZ	ADG719BRT-REEL
ADG508FBN	ADG601BRMZ	ADG659YRQ	ADG721ACPZ-REEL
ADG508FBNZ	ADG601BRTZ-REEL	ADG659YRU	ADG721BRM
ADG508FBRN	ADG602BRM	ADG663BRU	ADG722ACPZ-REEL
ADG508FBRUZ	ADG602BRTZ-REEL	ADG701BRJ-500RL7	ADG722BRM
ADG508FBRW	ADG604YRU	ADG701BRM	ADG723ACPZ-REEL
ADG508FTQ	ADG604YRUZ	ADG701BRTZ-REEL	ADG723BRM
ADG509FBN	ADG608BN	ADG701LBRJZ-REEL7	ADG741BKSZ5-REEL
ADG509FBRN	ADG608BR	ADG701LBRMZ	ADG741BKSZ-REEL
ADG509FBRUZ	ADG608BRU	ADG701LBRTZ-REEL7	ADG742BKSZ5-REEL
ADG509FBRW	ADG608TRU	ADG702BRJ-REEL7	ADG742BKSZ-R2
ADG509FBRWZ	ADG609BN	ADG702BRM	ADG749BKSZ-REEL
ADG509FTQ	ADG609BR	ADG702BRTZ-REEL	ADG779BKSZ-R2
ADG511BN	ADG609BRU	ADG702LBRJ-REEL	ADG781BCP
ADG511BR	ADG609BRUZ	ADG702LBRMZ	ADG782BCP
ADG511TQ	ADG609BRZ	ADG702LBRTZ-REEL7	ADG783BCP
ADG512BN	ADG611YRUZ	ADG711BR	ADG787BCBZ-REEL
ADG512BR	ADG611YRZ	ADG711BRU	ADG787BCPZ-REEL
ADG512TQ	ADG612WYRUZ-REEL	ADG712BR	ADG787BRMZ
ADG513BN	ADG612YRUZ	ADG712BRU	ADG801BRM
ADG513BR	ADG613YRUZ	ADG713BR	ADG801BRT-500RL7
ADG513TQ	ADG658YCPZ	ADG713BRU	ADG802BCBZ-REEL7
ADG528F	ADG658YRQ	ADG719BRM	ADG802BRM
ADG528FBN	ADG658YRU		
ADG528FBP			

Multisim 14.1 Base Edition Components

ADG802BRT-500RL7	ADR3425ARJZ-R2	ADSP-2103-TQFP(80)	ADSP-2163-TQFP(80)
	ADR3425ARJZ-R7		
ADG811YCPZ-REEL	ADR5040AKSZ-R2	ADSP-2105-PLCC(68)	ADSP-2164-PLCC(68)
ADG811YRU	ADR5040ARTZ-R2	ADSP-2111-PGA(100)	ADSP-2164-PQFP(80)
ADG812YRU	ADR5040BKSZ-R2	ADSP-2111-PQFP(100)	ADSP-2164-TQFP(80)
ADG813YRU	ADR5040BRTZ-R2	ADSP-2115-PLCC(68)	ADSP-2191M-LQFP(144)
ADG819BCB	ADR5041AKSZ-R2	ADSP-2115-PQFP(80)	ADTL082ARMZ
ADG819BRM	ADR5041ARTZ-R2	ADSP-2115-TQFP(80)	ADTL082ARZ
ADG819BRT	ADR5041BKSZ-R2	ADSP-2161-PLCC(68)	ADTL082JR
ADG820BRM	ADR5041BRTZ-R2	ADSP-2161-PQFP(80)	ADTL082JRZ
ADG820BRT	ADR5041WARTZ-R7	ADSP-2162-PLCC(68)	ADTL084ARUZ
ADG821BRM	ADR5041WBRTZ-R7	ADSP-2162-PQFP(80)	ADTL084ARZ
ADG822BRM	ADS8320EB	ADSP-2162-TQFP(80)	ADTL084JR
ADG823BRM	ADS8322YB	ADSP-2162-TQFP(80)	ADTL084JRZ
ADG839YKSZ-500RL7	ADS8364Y	ADSP-2162-PLCC(68)	ADZS-BRKOUT-EX3
ADG841YKSZ-500RL7	ADSP-2101-PGA(68)	ADSP-2162-PQFP(80)	AIR_NC
ADG842YKSZ-500RL7	ADSP-2101-PLCC(68)	ADSP-2162-PQFP(80)	AIR_NO
ADG849YKSZ-500RL7	ADSP-2101-PQFP(80)	ADSP-2162-TQFP(80)	ALM2402QDRRRQ1
ADG859BRYZ-REEL	ADSP-2101-TQFP(80)	ADSP-2163-PLCC(68)	ALM2402QPWPRQ1
ADG859YRYZ-REEL	ADSP-2103-PLCC(68)	ADSP-2163-PLCC(68)	1
ADG884BCBZ-REEL	ADSP-2103-PQFP(80)	ADSP-2163-PQFP(80)	ALPHA_NUMERIC_COM_A_BLUE
ADG884BCPZ-REEL			ALPHA_NUMERIC_COM_A_GREEN
ADG884BRMZ			

Multisim 14.1 Base Edition Components

ALPHA_NUMERIC_COM_A_ORANGE	AM29521AJC	AND2	ASSR-V621-302E
ALPHA_NUMERIC_COM_A_RED	AM29521ALC	AND2	ASSR-V622-002E
ALPHA_NUMERIC_COM_A_YELLOW	AM29521APC	AND3	ASSR-V622-302E
ALPHA_NUMERIC_COM_K_BLUE	AM29521APCB	AND3	ATF750C-10PC
ALPHA_NUMERIC_COM_K_GREEN	AM29LV800BB-70EI	AND4	ATF750C-10XC
ALPHA_NUMERIC_COM_K_ORANGE	AMMETER_H	AND4	ATF750C-15PC
ALPHA_NUMERIC_COM_K_RED	AMMETER_HR	AND5	ATF750C-15XC
ALPHA_NUMERIC_COM_K_YELLOW	AMMETER_V	AND5	ATF750CL-15PC
ALTERA-BYTEBLASTER-HDR	AMMETER_VR	AND6	ATF750CL-15XC
ALU_4BIT	AMP01AX	AND6	ATP207-TL-H
AM_VOLTAGE	AMP01BX	AND7	ATP301-TL-H
AM29520ADC	AMP01EX	AND7	ATP405-TL-H
AM29520ADCB	AMP01FX	AND8	ATV2500BL-20JI
AM29520AJC	AMP01GS	AND8	ATV2500BQ-20JC
AM29520ALC	AMP02AZ	ANTI_PLUG	AVR-JTAG-HDR
AM29520APC	AMP02EP	ARBITRARY_LAPLAC_E_FUNCTION	B6S-E3/80
AM29520APCB	AMP02FP	ARBITRARY_SPICE_BLOCK	BA157GP
AM29521ADC	AMP02FS	ARM-14-HDR	BA158GP
AM29521ADCB	AMP04EP	ARM-20-HDR	BA159-E3/54
	AMP04ES	ASP-134488-01	BA159GP
	AMP04FP	ASP-134603-01	BA220
	AMP04FS	ASP-134604-01	BA221
	ANALOG_SWITCH_VIRTUAL	ASP-134606-01	BA223
	AND_OR_I	ASSR-V621-002E	BA281
			BA314

Multisim 14.1 Base Edition Components

BA315	BAR_LED_GREEN_FOUR	BAR63-04	BAS116QA
BA316		BAR63-04W	BAS116T
BA317	BAR_LED_GREEN_TEN	BAR63-05	BAS116TT1G
BA318	BAR_LED_ORANGE	BAR63-05W	BAS125-04W
BA423	BAR_LED_ORANGE_FOUR	BAR63-06	BAS125-05W
BA423L		BAR63-06W	BAS125-07W
BA481	BAR_LED_ORANGE_TEN	BAR64-02V	BAS140W
BA482	BAR_LED_RED	BAR64-03W	BAS15
BA483	BAR_LED_RED_FOUR	BAR64-04	BAS16
BA484		BAR64-04W	BAS16-02L
BA592	BAR_LED_RED_TEN	BAR64-05W	BAS16DXV6T1G
BA595	BAR_LED_YELLOW	BAR64-06W	BAS16H
BA682	BAR_LED_YELLOW_FOUR	BAR65-03W	BAS16J
BA683		BAR67-02V	BAS16L
BA885	BAR_LED_YELLOW_TEN	BAR74	BAS16LD
BA892	BAR14-1	BAR81W	BAS16M3T5G
BA895	BAR15-1	BAR88-02V	BAS16P2T5G
BAL74	BAR16-1	BAR99	BAS16QA
BAL99	BAR50-02L	BAS101	BAS16T
BAR_LED_BLUE	BAR50-02V	BAS101S	BAS16VV
BAR_LED_BLUE_FOUR	BAR61	BAS11	BAS16VY
BAR_LED_BLUE_TEN	BAR63-02L	BAS116	BAS16W
	BAR63-02V	BAS116H	BAS17
BAR_LED_GREEN	BAR63-02W	BAS116L	BAS170W
	BAR63-03W	BAS116LT1G	BAS19

Multisim 14.1 Base Edition Components

BAS20	BAS35	BAS70-02L	BAT120S
BAS20HT1G	BAS40	BAS70-02W	BAT15-02LRH
BAS20LT1G	BAS40-02L	BAS70-04	BAT15-03W
BAS21	BAS40-04	BAS70-04LT1G	BAT15-04W
BAS21AVD	BAS40-05	BAS70-04W	BAT15-05W
BAS21AW	BAS40-05V	BAS70-05	BAT15-099
BAS21H	BAS40-05W	BAS70-05W	BAT160A
BAS21HT1G	BAS40-06	BAS70-06	BAT160C
BAS21J	BAS40-06W	BAS70-06W	BAT160S
BAS21M3T5G	BAS40-07	BAS70-07	BAT165
BAS21SLT1G	BAS40-07V	BAS70-07S	BAT165A
BAS21SW	BAS40-07W	BAS70-07V	BAT17
BAS21TMR6T1G	BAS40H	BAS70H	BAT17-04
BAS21U	BAS40L	BAS70L	BAT17-05
BAS21VD	BAS40W	BAS70VV	BAT17-05W
BAS21W	BAS40XY	BAS70W	BAT17-06W
BAS28	BAS416	BAS70XY	BAT17-07
BAS29	BAS45	BAS716	BAT18
BAS3010B-03W	BAS45A	BAS81	BAT18-04
BAS3020B	BAS45AL	BAS82	BAT18-05
BAS31	BAS45L	BAS83	BAT24-02LS
BAS316	BAS516	BAS85	BAT240A
BAS32	BAS521	BAS86	BAT46WH
BAS321	BAS56	BAT120A	BAT46WJ
BAS32L	BAS70	BAT120C	BAT54

Multisim 14.1 Base Edition Components

BAT54A	BAT62-02W	BAT754	BAV18
BAT54AW	BAT62-03W	BAT754A	BAV19
BAT54C	BAT62-07W	BAT754C	BAV199
BAT54CLT1	BAT63-07W	BAT754L	BAV199W
BAT54CLT1G	BAT64	BAT754S	BAV20
BAT54CLT3G	BAT64-02W	BAT760	BAV21
BAT54CM	BAT64-04	BAT81	BAV23
BAT54CV	BAT64-04W	BAT82	BAV23A
BAT54CW	BAT64-05	BAT83	BAV23C
BAT54H	BAT64-05W	BAT85	BAV23S
BAT54J	BAT64-06	BAT854AW	BAV45
BAT54L	BAT64-06W	BAT854CW	BAV70
BAT54LT1G	BAT68	BAT854SW	BAV70DXV6T5G
BAT54M3T5G	BAT68-04	BAT854W	BAV70LT1
BAT54S	BAT68-04W	BAT86	BAV70LT1G
BAT54SW	BAT68-06	BAT960	BAV70LT3G
BAT54T	BAT68-06W	BAV10	BAV70M
BAT54VV	BAT720	BAV100	BAV70M3T5G
BAT54W	BAT721	BAV101	BAV70QA
BAT54WT1G	BAT721A	BAV102	BAV70S
BAT54XY	BAT721C	BAV103	BAV70T
BAT60A	BAT721S	BAV105	BAV70TT1G
BAT60B	BAT74	BAV170	BAV70W
BAT62	BAT74S	BAV170M	BAV74
BAT62-02L	BAT74V	BAV170QA	BAV74LT1

Multisim 14.1 Base Edition Components

BAV74LT1G	BAX12	BB619	BBY31
BAV756S	BAX14	BB620	BBY39
BAV99	BAX18	BB639	BBY40
BAV99LT1	BAY80	BB639C	BBY42
BAV99LT1G	BB112	BB640	BBY51-02W
BAV99LT3	BB119	BB644	BBY51-03W
BAV99LT3G	BB130	BB659	BBY52-02L
BAV99QA	BB204B	BB659C	BBY52-02W
BAV99S	BB204G	BB659C-02V	BBY53-02L
BAV99W	BB212	BB664	BBY53-02V
BAW101	BB215	BB664-02V	BBY53-02W
BAW101S	BB219	BB689	BBY53-03W
BAW156	BB240	BB689-02V	BBY53-05W
BAW56	BB241	BB804	BBY55-02V
BAW56LT1	BB249	BB809	BBY55-03W
BAW56LT1G	BB405B	BB811	BBY56-02W
BAW56LT3G	BB417	BB814	BBY56-03W
BAW56M	BB439	BB833	BBY57-02V
BAW56M3T5G	BB515	BB837	BBY57-02W
BAW56QA	BB535	BB857	BBY57-05W
BAW56S	BB545	BB909A	BBY58-02V
BAW56T	BB555	BB909B	BBY58-02W
BAW56TT1G	BB555-02V	BB910	BBY58-03W
BAW56W	BB565	BB911	BBY58-05W
BAW62	BB565-02V	BB914	BBY58-06W

Multisim 14.1 Base Edition Components

BBY62	BC413BP	BC54-16PAS	BC56-10PA
BBY65-02V	BC414BP	BC546BP	BC56-10PAS
BBY66-02V	BC415AP	BC547BG	BC56-16PA
BBY66-05W	BC416AP	BC547BP	BC56-16PAS
BC107BP	BC51-10PA	BC547BRL1G	BC56PA
BC108BP	BC51-10PAS	BC547BZL1G	BC56PAS
BC109BP	BC51-16PA	BC548BP	BC68-25PA
BC177AP	BC51-16PAS	BC549BP	BC68-25PAS
BC178AP	BC51PA	BC54PA	BC68PA
BC182BP	BC51PAS	BC54PAS	BC68PAS
BC183BP	BC52-10PA	BC550BP	BC69-16PA
BC184BP	BC52-10PAS	BC55-10PA	BC69-16PAS
BC212AP	BC52-16PA	BC55-10PAS	BC69-25PA
BC213AP	BC52-16PAS	BC55-16PA	BC69-25PAS
BC237BP	BC52PA	BC55-16PAS	BC69PA
BC238BP	BC52PAS	BC556AP	BC69PAS
BC239BP	BC53-10PA	BC557AP	BC807
BC264A	BC53-10PAS	BC557BG	BC807-16
BC264B	BC53-16PA	BC557BRL1G	BC807-16LT1G
BC264C	BC53-16PAS	BC557BZL1G	BC807-16LT3G
BC264D	BC53PA	BC558AP	BC807-16W
BC307AP	BC53PAS	BC559AP	BC807-25
BC308AP	BC54-10PA	BC55PA	BC807-25LT1G
BC337AP	BC54-10PAS	BC55PAS	BC807-25LT3G
BC338AP	BC54-16PA	BC560AP	BC807-25QA

Multisim 14.1 Base Edition Components

BC807-25W	BC846A	BC847AQA	BC847CQA
BC807-40	BC846ALT1G	BC847AT	BC847CT
BC807-40LT1G	BC846ALT3G	BC847AW	BC847CTT1G
BC807-40LT3G	BC846AT	BC847B	BC847CW
BC807-40QA	BC846AW	BC847BDW1T1G	BC847DS
BC807-40W	BC846B	BC847BDW1T3	BC847QAPN
BC807DS	BC846BDW1T1G	BC847BDW1T3G	BC847QAS
BC807W	BC846BLT1G	BC847BM	BC847T
BC808-16	BC846BLT3G	BC847BMB	BC847W
BC817	BC846BM	BC847BPDW1T1	BC848B
BC817-16	BC846BM3T5G	BC847BPDW1T1G	BC848W
BC817-16W	BC846BMB	BC847BPDW1T2G	BC849B
BC817-25	BC846BPDW1T1G	BC847BPDW1T3G	BC849BW
BC817-25LT1	BC846BPN	BC847BPDV6T1G	BC849C
BC817-25LT1G	BC846BS	BC847BPN	BC849CW
BC817-25LT3G	BC846BT	BC847BQA	BC850B
BC817-25QA	BC846BW	BC847BS	BC850BW
BC817-25W	BC846DS	BC847BT	BC850C
BC817-40	BC846S	BC847BV	BC850CW
BC817-40QA	BC846T	BC847BVN	BC856
BC817-40W	BC846W	BC847BW	BC856A
BC817DPN	BC847	BC847C	BC856ALT1G
BC817DS	BC847A	BC847CDV6T1G	BC856AT
BC817W	BC847AM	BC847CM	BC856AW
BC846	BC847AMB	BC847CMB	BC856B

Multisim 14.1 Base Edition Components

BC856BDW1T1G	BC857BV	BC868-25	BCP53-16
BC856BDW1T3G	BC857BW	BC869	BCP54
BC856BM	BC857C	BC869-16	BCP54-10
BC856BMB	BC857CM	BC869-25	BCP54-16
BC856BS	BC857CMB	BCD_7SEG_DCD	BCP55
BC856BT	BC857CQA	BCM61B	BCP55-10
BC856BW	BC857CT	BCM62B	BCP55-16
BC856BWT1G	BC857CW	BCM846BS	BCP56
BC856S	BC857QAS	BCM847BS	BCP56-10
BC856T	BC857T	BCM847BV	BCP56-10T1
BC856W	BC857W	BCM847DS	BCP56-10T1G
BC857	BC858A	BCM856BS	BCP56-10T3G
BC857A	BC858B	BCM856DS	BCP56-16
BC857AM	BC858W	BCM857BS	BCP56-16T1
BC857AMB	BC859A	BCM857BV	BCP56-16T1G
BC857AQA	BC859B	BCM857DS	BCP56-16T3G
BC857AT	BC859BW	BCP49	BCP56T1
BC857AW	BC859C	BCP51	BCP56T1G
BC857B	BC859CW	BCP51-10	BCP56T3G
BC857BDW1T1G	BC860A	BCP51-16	BCP68
BC857BM	BC860B	BCP52	BCP68-25
BC857BMB	BC860BW	BCP52-10	BCP68T1G
BC857BQA	BC860C	BCP52-16	BCP69
BC857BS	BC860CW	BCP53	BCP69-16
BC857BT	BC868	BCP53-10	BCP69-25

Multisim 14.1 Base Edition Components

BCP69T1G	BCR141W	BCR196	BCV47
BCR08PN	BCR142	BCR196W	BCV48
BCR108	BCR142W	BCR198	BCV49
BCR108S	BCR146	BCR198S	BCV61
BCR108W	BCR148	BCR198W	BCV61A
BCR10PN	BCR148S	BCR22PN	BCV61B
BCR112	BCR148W	BCR35PN	BCV61C
BCR112W	BCR158	BCR48PN	BCV62
BCR116	BCR158W	BCR503	BCV62A
BCR116S	BCR162	BCR505	BCV62B
BCR116W	BCR166	BCR512	BCV62C
BCR119	BCR166W	BCR521	BCV63
BCR119S	BCR169	BCR523	BCV63B
BCR119W	BCR169S	BCR523U	BCV64B
BCR129	BCR169W	BCR533	BCV65
BCR129S	BCR183	BCR553	BCV71
BCR129W	BCR183S	BCR555	BCV72
BCR133	BCR183W	BCR562	BCW29
BCR133S	BCR185	BCR573	BCW30
BCR133W	BCR185S	BCR583	BCW31
BCR135	BCR185W	BCV26	BCW32
BCR135S	BCR191	BCV27	BCW33
BCR135W	BCR191W	BCV28	BCW60B
BCR141	BCR192	BCV29	BCW60C
BCR141S	BCR192W	BCV46	BCW60D

Multisim 14.1 Base Edition Components

BCW61A	BCX52-16	BD137	BD441G
BCW61B	BCX53	BD137G	BD442G
BCW61C	BCX53-10	BD138	BD675AG
BCW61D	BCX53-16	BD138G	BD675G
BCW65A	BCX54	BD139	BD676AG
BCW66F	BCX54-10	BD139G	BD676G
BCW67A	BCX54-16	BD140	BD677AG
BCW68F	BCX55	BD140G	BD677G
BCW69	BCX55-10	BD159G	BD678AG
BCW70	BCX55-16	BD179G	BD678G
BCW71	BCX56	BD180G	BD679AG
BCW72	BCX56-10	BD234G	BD679G
BCW89	BCX56-16	BD237G	BD680AG
BCX17	BCX70G	BD241CG	BD680G
BCX17LT1G	BCX70H	BD242BG	BD681G
BCX18	BCX70J	BD242CG	BD682G
BCX19	BCX70K	BD243CG	BD787G
BCX38B	BCX71G	BD244BG	BD788G
BCX41	BCX71H	BD244CG	BD809G
BCX42	BCX71J	BD436TG	BD810G
BCX51	BCX71K	BD437G	BDP947
BCX51-10	BD135	BD437TG	BDP948
BCX51-16	BD135G	BD438G	BDP949
BCX52	BD136	BD439G	BDP950
BCX52-10	BD136G	BD440G	BDP953

Multisim 14.1 Base Edition Components

BDP954	BF422G	BF823	BFN24
BDV64BG	BF510	BF824	BFN26
BDV65BG	BF511	BF824W	BFN27
BDW42G	BF512	BF840	BFN38
BDW46G	BF513	BF851A	BFN39
BDW47G	BF517	BF851B	BFP194
BDX33BG	BF545A	BF851C	BFQ31
BDX33CG	BF545B	BF861A	BFR194
BDX34BG	BF545C	BF861B	BFR30
BDX34CG	BF550	BF861C	BFR31
BDX53BG	BF556A	BF904	BFS17
BDX53CG	BF556B	BF904R	BFS17H
BDX54BG	BF570	BF904WR	BFS17P
BDX54CG	BF620	BF908WR	BFS19
BF245A	BF621	BF909	BFS20
BF245B	BF622	BF909R	BFS20W
BF245C	BF623	BF909WR	BFS60
BF246A	BF720	BF998	BFT46
BF247A	BF722	BF998R	BFU308
BF256A	BF723	BF998WR	BFU309
BF256B	BF799	BFG135A	BFU310
BF410A	BF820	BFG193	BFW10
BF410B	BF820W	BFG194	BFW11
BF410C	BF821	BFN18	BFW12
BF410D	BF822	BFN19	BFW13

Multisim 14.1 Base Edition Components

BFW61	BS170	BSC014N06NS	BSC030N03MS G
BICOLOR_LED_Red/ Green	BSB008NE2LX	BSC014NE2LSI	BSC030N04NS G
BICOLOR_LED_Red- Orange/Green	BSB012N03LX3 G	BSC016N03LS G	BSC030P03NS3 G
BIPOLAR_CURRENT	BSB012NE2LX	BSC016N03MS G	BSC031N06NS3 G
BIPOLAR_VOLTAGE	BSB012NE2LXI	BSC016N04LS G	BSC032N04LS
BJT_LPNP	BSB013NE2LXI	BSC016N06NS	BSC032NE2LS
BJT_NPN	BSB014N04LX3 G	BSC017N04NS G	BSC034N06NS
BJT_NPN_4T	BSB015N04NX3 G	BSC018N04LS G	BSC035N04LS G
BJT_PNP	BSB017N03LX3 G	BSC018NE2LS	BSC036NE7NS3 G
BJT_PNP_4T	BSB028N06NN3 G	BSC018NE2LSI	BSC039N06NS
BOOST_CONVERTER	BSB044N08NN3 G	BSC019N02KS G	BSC042N03LS G
R	BSB056N10NN3 G	BSC019N04LS	BSC042N03MS G
BOSCH-EDC16- BDM-HDR	BSB165N15NZ3 G	BSC019N04NS G	BSC042NE7NS3 G
BPASS	BSB280N15NZ3 G	BSC020N03LS G	BSC046N02KS G
BPV10NF	BSC009NE2LS	BSC020N03MS G	BSC046N10NS3 G
BPV22NF	BSC010N04LS	BSC022N04LS	BSC047N08NS3 G
BPV23F	BSC010N04LSI	BSC024NE2LS	BSC050N03LS G
BPV23NF	BSC010NE2LS	BSC025N03LS G	BSC050N03MS G
BPW 34	BSC010NE2LSI	BSC025N03MS G	BSC050N04LS G
BPW 34 FA	BSC011N03LS	BSC026N02KS G	BSC050NE2LS
BPW 34 FAS	BSC011N03LSI	BSC026N04LS	BSC052N03LS
BPW 34 FASR	BSC014N03LS G	BSC027N04LS G	BSC054N04NS G
BRUSHLESS_DC_M ACHINE	BSC014N03MS G	BSC028N06LS3 G	BSC057N03LS G
	BSC014N04LS	BSC028N06NS	BSC057N03MS G
	BSC014N04LSI	BSC030N03LS G	BSC057N08NS3 G

Multisim 14.1 Base Edition Components

BSC059N04LS G	BSC090N03MS G	BSC159N10LSF G	BSD235N
BSC060N10NS3 G	BSC0910NDI	BSC160N10NS3 G	BSD314SPE
BSC060P03NS3E G	BSC0911ND	BSC16DN25NS3 G	BSD316SN
BSC066N06NS	BSC0921NDI	BSC190N12NS3 G	BSD816SN
BSC067N06LS3 G	BSC0923NDI	BSC190N15NS3 G	BSD840N
BSC070N10NS3 G	BSC0924NDI	BSC196N10NS G	BSE-080-01-L-D-A
BSC072N03LD G	BSC0925ND	BSC200P03LS G	BSF024N03LT3 G
BSC076N06NS3 G	BSC093N04LS G	BSC205N10LS G	BSF030NE2LQ
BSC077N12NS3 G	BSC097N06NS	BSC22DN20NS3 G	BSF035NE2LQ
BSC079N10NS G	BSC100N03LS G	BSC240N12NS3 G	BSF050N03LQ3 G
BSC080N03LS G	BSC100N03MS G	BSC252N10NSF G	BSF134N10NJ3 G
BSC080N03MS G	BSC100N06LS3 G	BSC265N10LSF G	BSF450NE7NH3 G
BSC080P03LS G	BSC100N10NSF G	BSC320N20NS3 G	BSH103
BSC082N10LS G	BSC105N10LSF G	BSC340N08NS3 G	BSH105
BSC084P03NS3 G	BSC109N10NS3 G	BSC360N15NS3 G	BSH108
BSC084P03NS3E G	BSC110N06NS3 G	BSC440N10NS3 G	BSH111
BSC0901NS	BSC118N10NS G	BSC500N20NS3 G	BSH111BK
BSC0901NSI	BSC120N03LS G	BSC520N15NS3 G	BSH114
BSC0902NS	BSC120N03MS G	BSC600N25NS3 G	BSH121
BSC0902NSI	BSC123N08NS3 G	BSC750N10ND G	BSH201
BSC0904NSI	BSC123N10LS G	BSC900N20NS3 G	BSH202
BSC0906NS	BSC12DN20NS3 G	BSD214	BSH203
BSC0908NS	BSC130P03LS G	BSD214SN	BSH205
BSC0909NS	BSC150N03LD G	BSD215	BSH207
BSC090N03LS G	BSC152N10NSF G	BSD223P	BSJ108

Multisim 14.1 Base Edition Components

BSJ109	BSO040N03MS G	BSP110	BSP32
BSJ110	BSO051N03MS G	BSP123	BSP324
BSL202SN	BSO065N03MS G	BSP125	BSP33
BSL205N	BSO080P03NS3 G	BSP129	BSP41
BSL207N	BSO080P03NS3E G	BSP135	BSP43
BSL207SP	BSO080P03S H	BSP149	BSP50
BSL211SP	BSO083N03MS G	BSP16T1G	BSP51
BSL214N	BSO110N03MS G	BSP170P	BSP52
BSL302SN	BSO130N03MS G	BSP171P	BSP52T1G
BSL306N	BSO130P03S H	BSP19	BSP52T3G
BSL307SP	BSO150N03MD G	BSP19AT1G	BSP60
BSL308PE	BSO200P03S H	BSP204	BSP61
BSL314PE	BSO201SP H	BSP204A	BSP613P
BSL606SN	BSO203SP H	BSP205	BSP62
BSL802SN	BSO207P H	BSP206	BSP88
BSL806N	BSO211P H	BSP230	BSP89
BSN011NE2LS	BSO220N03MD G	BSP250	BSP92P
BSN011NE2LSI	BSO220N03MS G	BSP296	BSR14
BSN012N03LS	BSO301SP H	BSP297	BSR16
BSN012N03LSI	BSO303SP H	BSP304	BSR19A
BSN045NE2LS	BSO330N02K G	BSP304A	BSR202N
BSN048N03LS	BSO613SPV G	BSP31	BSR30
BSN20	BSP 60 E6327	BSP315P	BSR302N
BSN20BK	BSP030	BSP316P	BSR31
BSO033N03MS G	BSP100	BSP317P	BSR315P

Multisim 14.1 Base Edition Components

BSR316P	BSS138W	BSS83P	BST62
BSR33	BSS139	BSS84	BST82
BSR41	BSS159N	BSS84AK	BSV236SP
BSR43	BSS169	BSS84AKM	BSV52
BSR56	BSS192	BSS84AKMB	BSV78
BSR57	BSS192P	BSS84AKS	BSV79
BSR58	BSS205N	BSS84AKT	BSV80
BSR606N	BSS209PW	BSS84AKV	BSV81
BSR802N	BSS214N	BSS84AKW	BSZ018NE2LS
BSR92P	BSS214NW	BSS84LT1G	BSZ018NE2LSI
BSS110	BSS223PW	BSS84P	BSZ019N03LS
BSS123	BSS225	BSS84PW	BSZ023N04LS
BSS123LT1G	BSS306N	BSS84PW H6327	BSZ028N04LS
BSS126	BSS308PE	BSS87	BSZ034N04LS
BSS127	BSS314PE	BSS92	BSZ035N03LS G
BSS131	BSS315P	BST100	BSZ035N03MS G
BSS138BK	BSS316N	BST110	BSZ036NE2LS
BSS138BKS	BSS606N	BST120	BSZ040N04LS G
BSS138BKW	BSS63	BST122	BSZ042N04NS G
BSS138LT1G	BSS64	BST39	BSZ042N06NS
BSS138LT3G	BSS670S2L	BST50	BSZ050N03LS G
BSS138N	BSS7728N	BST51	BSZ050N03MS G
BSS138P	BSS806N	BST52	BSZ058N03LS G
BSS138PS	BSS816NW	BST60	BSZ058N03MS G
BSS138PW	BSS83	BST61	BSZ060NE2LS

Multisim 14.1 Base Edition Components

BSZ065N03LS	BSZ123N08NS3 G	BT136-F	BTW40_400R
BSZ067N06LS3 G	BSZ12DN20NS3 G	BT136-G	BTW42_600R
BSZ068N06NS	BSZ130N03LS G	BT137	BTW43
BSZ076N06NS3 G	BSZ130N03MS G	BT137-E	BTW45_400R
BSZ086P03NS3 G	BSZ150N10LS3 G	BT137-F	BTY79_400R
BSZ086P03NS3E G	BSZ160N10NS3 G	BT137-G	BTY91_400R
BSZ088N03LS G	BSZ165N04NS G	BT138	BU323ZG
BSZ088N03MS G	BSZ16DN25NS3 G	BT138-E	BU406G
BSZ0901NS	BSZ180P03NS3 G	BT138-F	BUB323ZG
BSZ0901NSI	BSZ180P03NS3E G	BT138-G	BUB323ZT4G
BSZ0902NS	BSZ22DN20NS3 G	BT139	BUCK_BOOST_CONVERTER
BSZ0902NSI	BSZ240N12NS3 G	BT139-E	BUCK_CONVERTER
BSZ0904NSI	BSZ340N08NS3 G	BT139-F	BUD42D-1G
BSZ0907ND	BSZ42DN25NS3 G	BT139-G	BUD42DT4G
BSZ0908ND	BSZ440N10NS3 G	BT145_500R	BUF
BSZ0909NS	BSZ520N15NS3 G	BT148_400R	BUF_3S_AHOE
BSZ097N04LS G	BSZ900N15NS3 G	BT148W_400R	BUF_3S_ALOE
BSZ100N03LS G	BSZ900N20NS3 G	BT149_B	BUF_CO
BSZ100N03MS G	BT134	BT150_500R	BUF_INV
BSZ100N06LS3 G	BT134-E	BT151_500R	BUF601AP
BSZ100N06NS	BT134-F	BT152_400R	BUF602ID
BSZ105N04NS G	BT134-G	BT153_500R	BUF602IDBVR
BSZ110N06NS3 G	BT134W	BT169_B	BUF602IDG4
BSZ120P03NS3 G	BT136	BTA140	BUFFER
BSZ120P03NS3E G	BT136-E	BTW38_600R	

Multisim 14.1 Base Edition Components

BUH100G	BY712	BYD14J	BYD37M
BUH150G	BY713	BYD14K	BYD73A
BUH50G	BY714	BYD14M	BYD73B
BUL45D2G	BY715	BYD17D	BYD73C
BUL45G	BY716	BYD17G	BYD73D
BUV21G	BY717	BYD17J	BYD73E
BUV22G	BY718	BYD17K	BYD73F
BUV26G	BY719	BYD17M	BYD73G
BUX85G	BY720	BYD31D	BYD74A
BUZZER	BY721	BYD31G	BYD74B
BVSS123LT1G	BY722	BYD31J	BYD74C
BVSS138LT1G	BY723	BYD33D	BYD74D
BY228	BYD11	BYD33G	BYD74E
BY328	BYD11D	BYD33J	BYD74F
BY438	BYD11G	BYD33K	BYD74G
BY448	BYD11J	BYD33M	BYD77A
BY458	BYD11K	BYD34D	BYD77B
BY505	BYD11M	BYD34G	BYD77C
BY527	BYD13D	BYD34J	BYD77D
BY584	BYD13G	BYD34K	BYD77E
BY627	BYD13J	BYD34M	BYD77F
BY705	BYD13K	BYD37D	BYD77G
BY706	BYD13M	BYD37G	BYG10G-E3/TR
BY710	BYD14D	BYD37J	BYG10J-E3/TR
BY711	BYD14G	BYD37K	BYG20J-E3/TR

Multisim 14.1 Base Edition Components

BYG21M-E3/TR	BYM26E	BYV28-150	BYX10G
BYG22D-E3/TR	BYM36A	BYV28-200	BYX110GP
BYG24J-E3/TR3	BYM36B	BYV28-50	BZA408B
BYM10-100	BYM36C	BYV32-200G	BZA418A
BYM10-1000	BYM36D	BYV36A	BZA420A
BYM10-1000-E3/97	BYM36E	BYV36B	BZA456A
BYM10-200	BYM56A	BYV36C	BZA462A
BYM10-400	BYM56B	BYV36D	BZA820A
BYM10-50	BYM56C	BYV36E	BZA856A
BYM10-600	BYM56D	BYV95A	BZA856AL
BYM10-800	BYM56E	BYV95B	BZA856AVL
BYM11-100	BYS10-45-E3/TR	BYV95C	BZA862A
BYM11-1000	BYS11-90-E3/TR	BYV96D	BZA862AL
BYM11-1000-E3/96	BYT28-300-E3/45	BYV96E	BZA862AVL
BYM11-100-E3/96	BYV10-20	BYW29-200G	BZA868A
BYM11-200	BYV10-30	BYW51-200G	BZA868AL
BYM11-400	BYV10-40	BYW54	BZA868AVL
BYM11-50	BYV26A	BYW55	BZA956A
BYM11-600	BYV26B	BYW56	BZA956AVL
BYM11-800	BYV26C	BYW80-200G	BZA962A
BYM12-400-E3/96	BYV26D	BYW95A	BZA962AVL
BYM26A	BYV26E	BYW95B	BZA968A
BYM26B	BYV27-100	BYW95C	BZA968AVL
BYM26C	BYV27-50	BYW96D	BZB100A
BYM26D	BYV28-100	BYW96E	BZB784-C10

Multisim 14.1 Base Edition Components

BZB784-C11	BZB84-B18	BZB84-B6V2	BZB84-C3V6
BZB784-C12	BZB84-B20	BZB84-B6V8	BZB84-C3V9
BZB784-C13	BZB84-B22	BZB84-B75	BZB84-C43
BZB784-C15	BZB84-B24	BZB84-B7V5	BZB84-C47
BZB784-C2V4	BZB84-B27	BZB84-B8V2	BZB84-C4V3
BZB784-C2V7	BZB84-B2V4	BZB84-B9V1	BZB84-C4V7
BZB784-C3V0	BZB84-B2V7	BZB84-C10	BZB84-C51
BZB784-C3V3	BZB84-B30	BZB84-C11	BZB84-C56
BZB784-C3V6	BZB84-B33	BZB84-C12	BZB84-C5V1
BZB784-C3V9	BZB84-B36	BZB84-C13	BZB84-C5V6
BZB784-C4V3	BZB84-B39	BZB84-C15	BZB84-C62
BZB784-C4V7	BZB84-B3V0	BZB84-C16	BZB84-C68
BZB784-C5V1	BZB84-B3V3	BZB84-C18	BZB84-C6V2
BZB784-C5V6	BZB84-B3V6	BZB84-C20	BZB84-C6V8
BZB784-C6V2	BZB84-B3V9	BZB84-C22	BZB84-C75
BZB784-C6V8	BZB84-B43	BZB84-C24	BZB84-C7V5
BZB784-C7V5	BZB84-B47	BZB84-C27	BZB84-C8V2
BZB784-C8V2	BZB84-B4V3	BZB84-C2V4	BZB84-C9V1
BZB784-C9V1	BZB84-B4V7	BZB84-C2V7	BZB984-C10
BZB84-B10	BZB84-B51	BZB84-C30	BZB984-C11
BZB84-B11	BZB84-B56	BZB84-C33	BZB984-C12
BZB84-B12	BZB84-B5V1	BZB84-C36	BZB984-C13
BZB84-B13	BZB84-B5V6	BZB84-C39	BZB984-C15
BZB84-B15	BZB84-B62	BZB84-C3V0	BZB984-C2V4
BZB84-B16	BZB84-B68	BZB84-C3V3	BZB984-C2V7

Multisim 14.1 Base Edition Components

BZB984-C3V0	BZT52H-B2V7	BZT52H-C16	BZT52H-C6V2
BZB984-C3V3	BZT52H-B30	BZT52H-C18	BZT52H-C6V8
BZB984-C3V6	BZT52H-B33	BZT52H-C20	BZT52H-C75
BZB984-C3V9	BZT52H-B36	BZT52H-C22	BZT52H-C7V5
BZB984-C4V3	BZT52H-B39	BZT52H-C24	BZT52H-C8V2
BZB984-C4V7	BZT52H-B3V0	BZT52H-C27	BZT52H-C9V1
BZB984-C5V1	BZT52H-B43	BZT52H-C2V4	BZV49-C12
BZB984-C5V6	BZT52H-B47	BZT52H-C2V7	BZV49-C16
BZB984-C6V2	BZT52H-B51	BZT52H-C30	BZV49-C3V6
BZB984-C6V8	BZT52H-B56	BZT52H-C33	BZV55-B10
BZB984-C7V5	BZT52H-B5V1	BZT52H-C36	BZV55-B11
BZB984-C8V2	BZT52H-B5V6	BZT52H-C39	BZV55-B12
BZB984-C9V1	BZT52H-B62	BZT52H-C3V0	BZV55-B13
BZT52H-B10	BZT52H-B68	BZT52H-C3V6	BZV55-B15
BZT52H-B11	BZT52H-B6V2	BZT52H-C3V9	BZV55-B16
BZT52H-B12	BZT52H-B6V8	BZT52H-C43	BZV55-B18
BZT52H-B13	BZT52H-B75	BZT52H-C47	BZV55-B20
BZT52H-B15	BZT52H-B7V5	BZT52H-C4V3	BZV55-B22
BZT52H-B16	BZT52H-B8V2	BZT52H-C4V7	BZV55-B24
BZT52H-B18	BZT52H-B9V1	BZT52H-C51	BZV55-B27
BZT52H-B20	BZT52H-C10	BZT52H-C56	BZV55-B2V4
BZT52H-B22	BZT52H-C11	BZT52H-C5V1	BZV55-B2V7
BZT52H-B24	BZT52H-C12	BZT52H-C5V6	BZV55-B30
BZT52H-B27	BZT52H-C13	BZT52H-C62	BZV55-B33
BZT52H-B2V4	BZT52H-C15	BZT52H-C68	BZV55-B36

Multisim 14.1 Base Edition Components

BZV55-B39	BZV55-C16	BZV60-B13	BZV60-B5V6
BZV55-B3V0	BZV55-C18	BZV60-B15	BZV60-B62
BZV55-B3V3	BZV55-C27	BZV60-B16	BZV60-B68
BZV55-B3V6	BZV55-C2V4	BZV60-B18	BZV60-B6V2
BZV55-B3V9	BZV55-C2V7	BZV60-B20	BZV60-B6V8
BZV55-B43	BZV55-C33	BZV60-B22	BZV60-B75
BZV55-B47	BZV55-C3V0	BZV60-B24	BZV60-B7V5
BZV55-B4V3	BZV55-C3V3	BZV60-B27	BZV60-B8V2
BZV55-B4V7	BZV55-C3V6	BZV60-B2V4	BZV60-B9V1
BZV55-B51	BZV55-C3V9	BZV60-B2V7	BZV60-C10
BZV55-B56	BZV55-C43	BZV60-B30	BZV60-C11
BZV55-B5V1	BZV55-C47	BZV60-B33	BZV60-C12
BZV55-B5V6	BZV55-C4V3	BZV60-B36	BZV60-C13
BZV55-B68	BZV55-C4V7	BZV60-B39	BZV60-C15
BZV55-B6V2	BZV55-C5V1	BZV60-B3V0	BZV60-C16
BZV55-B6V8	BZV55-C5V6	BZV60-B3V3	BZV60-C18
BZV55-B75	BZV55-C6V2	BZV60-B3V6	BZV60-C20
BZV55-B7V5	BZV55-C6V8	BZV60-B3V9	BZV60-C22
BZV55-B8V2	BZV55-C7V5	BZV60-B43	BZV60-C24
BZV55-B9V1	BZV55-C8V2	BZV60-B47	BZV60-C27
BZV55-C10	BZV55-C9V1	BZV60-B4V3	BZV60-C2V4
BZV55-C11	BZV55-F2V4	BZV60-B4V7	BZV60-C2V7
BZV55-C12	BZV60-B10	BZV60-B51	BZV60-C30
BZV55-C13	BZV60-B11	BZV60-B56	BZV60-C33
BZV55-C15	BZV60-B12	BZV60-B5V1	BZV60-C36

Multisim 14.1 Base Edition Components

BZV60-C39	BZV85-C13	BZV85-C75	BZV90-C3V3
BZV60-C3V0	BZV85-C15	BZV85-C7V5	BZV90-C3V6
BZV60-C3V3	BZV85-C16	BZV85-C8V2	BZV90-C3V9
BZV60-C3V6	BZV85-C18	BZV86-1V4	BZV90-C43
BZV60-C3V9	BZV85-C20	BZV86-2V0	BZV90-C47
BZV60-C43	BZV85-C22	BZV86-2V6	BZV90-C4V3
BZV60-C47	BZV85-C24	BZV86-3V2	BZV90-C4V7
BZV60-C4V3	BZV85-C27	BZV90-C10	BZV90-C51
BZV60-C4V7	BZV85-C30	BZV90-C11	BZV90-C56
BZV60-C51	BZV85-C33	BZV90-C12	BZV90-C5V1
BZV60-C56	BZV85-C36	BZV90-C13	BZV90-C5V6
BZV60-C5V1	BZV85-C39	BZV90-C15	BZV90-C62
BZV60-C5V6	BZV85-C3V6	BZV90-C16	BZV90-C68
BZV60-C62	BZV85-C3V9	BZV90-C18	BZV90-C6V2
BZV60-C68	BZV85-C43	BZV90-C20	BZV90-C6V8
BZV60-C6V2	BZV85-C47	BZV90-C22	BZV90-C75
BZV60-C6V8	BZV85-C4V3	BZV90-C24	BZV90-C7V5
BZV60-C75	BZV85-C4V7	BZV90-C27	BZV90-C8V2
BZV60-C7V5	BZV85-C51	BZV90-C2V4	BZV90-C9V1
BZV60-C8V2	BZV85-C5V1	BZV90-C2V7	BZW03-C10
BZV60-C9V1	BZV85-C5V6	BZV90-C30	BZW03-C100
BZV80	BZV85-C62	BZV90-C33	BZW03-C11
BZV85-C10	BZV85-C68	BZV90-C36	BZW03-C110
BZV85-C11	BZV85-C6V2	BZV90-C39	BZW03-C12
BZV85-C12	BZV85-C6V8	BZV90-C3V0	BZW03-C120

Multisim 14.1 Base Edition Components

BZW03-C13	BZW03-C68	BZX384-B3V0	BZX384-C20
BZW03-C130	BZW03-C75	BZX384-B3V3	BZX384-C22
BZW03-C15	BZW03-C7V5	BZX384-B3V6	BZX384-C24
BZW03-C150	BZW03-C82	BZX384-B3V9	BZX384-C2V4
BZW03-C16	BZW03-C8V2	BZX384-B43	BZX384-C2V7
BZW03-C160	BZW03-C91	BZX384-B47	BZX384-C30
BZW03-C18	BZW03-C9V1	BZX384-B4V3	BZX384-C33
BZW03-C180	BZX100A	BZX384-B4V7	BZX384-C36
BZW03-C20	BZX384-B10	BZX384-B51	BZX384-C39
BZW03-C200	BZX384-B11	BZX384-B56	BZX384-C3V0
BZW03-C22	BZX384-B12	BZX384-B5V1	BZX384-C3V3
BZW03-C220	BZX384-B13	BZX384-B5V6	BZX384-C3V6
BZW03-C24	BZX384-B15	BZX384-B62	BZX384-C3V9
BZW03-C240	BZX384-B16	BZX384-B68	BZX384-C43
BZW03-C27	BZX384-B18	BZX384-B6V2	BZX384-C47
BZW03-C270	BZX384-B20	BZX384-B6V8	BZX384-C4V3
BZW03-C30	BZX384-B22	BZX384-B75	BZX384-C4V7
BZW03-C33	BZX384-B24	BZX384-B7V5	BZX384-C51
BZW03-C36	BZX384-B27	BZX384-B8V2	BZX384-C56
BZW03-C39	BZX384-B2V4	BZX384-B9V1	BZX384-C5V1
BZW03-C43	BZX384-B2V7	BZX384-C10	BZX384-C62
BZW03-C47	BZX384-B30	BZX384-C11	BZX384-C68
BZW03-C51	BZX384-B33	BZX384-C12	BZX384-C6V2
BZW03-C56	BZX384-B36	BZX384-C13	BZX384-C6V8
BZW03-C62	BZX384-B39	BZX384-C16	BZX384-C75

Multisim 14.1 Base Edition Components

BZX384-C7V5	BZX55C47	BZX585-B22	BZX585-B75
BZX384-C8V2	BZX55C4V3	BZX585-B24	BZX585-B7V5
BZX384-C9V1	BZX55C4V7	BZX585-B27	BZX585-B8V2
BZX55C10	BZX55C51	BZX585-B2V4	BZX585-B9V1
BZX55C11	BZX55C56	BZX585-B2V7	BZX585-C10
BZX55C12	BZX55C5V1	BZX585-B30	BZX585-C11
BZX55C13	BZX55C5V6	BZX585-B33	BZX585-C12
BZX55C15	BZX55C62	BZX585-B36	BZX585-C13
BZX55C16	BZX55C68	BZX585-B39	BZX585-C16
BZX55C18	BZX55C6V2	BZX585-B3V0	BZX585-C20
BZX55C20	BZX55C6V8	BZX585-B3V3	BZX585-C22
BZX55C22	BZX55C75	BZX585-B3V6	BZX585-C24
BZX55C24	BZX55C7V5	BZX585-B3V9	BZX585-C2V4
BZX55C27	BZX55C82	BZX585-B43	BZX585-C2V7
BZX55C2V4	BZX55C8V2	BZX585-B47	BZX585-C30
BZX55C2V7	BZX55C91	BZX585-B4V3	BZX585-C33
BZX55C30	BZX55C9V1	BZX585-B4V7	BZX585-C36
BZX55C33	BZX585-B10	BZX585-B51	BZX585-C39
BZX55C36	BZX585-B11	BZX585-B56	BZX585-C3V0
BZX55C39	BZX585-B12	BZX585-B5V1	BZX585-C3V3
BZX55C3V0	BZX585-B13	BZX585-B5V6	BZX585-C3V6
BZX55C3V3	BZX585-B15	BZX585-B62	BZX585-C3V9
BZX55C3V6	BZX585-B16	BZX585-B68	BZX585-C43
BZX55C3V9	BZX585-B18	BZX585-B6V2	BZX585-C47
BZX55C43	BZX585-B20	BZX585-B6V8	BZX585-C4V3

Multisim 14.1 Base Edition Components

BZX585-C4V7	BZX79-A30	BZX79-B11	BZX79-B5V1
BZX585-C51	BZX79-A33	BZX79-B12	BZX79-B62
BZX585-C56	BZX79-A36	BZX79-B13	BZX79-B68
BZX585-C5V1	BZX79-A3V0	BZX79-B15	BZX79-B6V2
BZX585-C62	BZX79-A3V3	BZX79-B16	BZX79-B6V8
BZX585-C68	BZX79-A3V6	BZX79-B18	BZX79-B75
BZX585-C6V2	BZX79-A3V9	BZX79-B20	BZX79-B7V5
BZX585-C6V8	BZX79-A40	BZX79-B22	BZX79-B8V2
BZX585-C75	BZX79-A43	BZX79-B24	BZX79-B9V1
BZX585-C7V5	BZX79-A47	BZX79-B27	BZX79-C10
BZX585-C8V2	BZX79-A4V3	BZX79-B2V4	BZX79-C100
BZX585-C9V1	BZX79-A4V7	BZX79-B2V7	BZX79-C11
BZX79-A10	BZX79-A51	BZX79-B30	BZX79-C110
BZX79-A11	BZX79-A56	BZX79-B33	BZX79-C12
BZX79-A12	BZX79-A5V1	BZX79-B36	BZX79-C120
BZX79-A13	BZX79-A5V6	BZX79-B39	BZX79-C13
BZX79-A15	BZX79-A62	BZX79-B3V3	BZX79-C130
BZX79-A16	BZX79-A68	BZX79-B3V6	BZX79-C15
BZX79-A18	BZX79-A6V2	BZX79-B3V9	BZX79-C150
BZX79-A20	BZX79-A6V8	BZX79-B43	BZX79-C16
BZX79-A22	BZX79-A75	BZX79-B47	BZX79-C160
BZX79-A24	BZX79-A7V5	BZX79-B4V3	BZX79-C18
BZX79-A27	BZX79-A8V2	BZX79-B4V7	BZX79-C180
BZX79-A2V4	BZX79-A9V1	BZX79-B51	BZX79-C20
BZX79-A2V7	BZX79-B10	BZX79-B56	BZX79-C200

Multisim 14.1 Base Edition Components

BZX79-C22	BZX79-C75	BZX83-C4V7	BZX84-A3V0
BZX79-C24	BZX79-C7V5	BZX83-C5V1	BZX84-A3V3
BZX79-C27	BZX79-C82	BZX83-C5V6	BZX84-A3V6
BZX79-C2V4	BZX79-C8V2	BZX83-C6V2	BZX84-A3V9
BZX79-C2V7	BZX79-C91	BZX83-C6V8	BZX84-A43
BZX79-C30	BZX79-C9V1	BZX83-C7V5	BZX84-A47
BZX79-C33	BZX83-C10	BZX83-C8V2	BZX84-A4V3
BZX79-C36	BZX83-C11	BZX83-C9V1	BZX84-A4V7
BZX79-C39	BZX83-C12	BZX84-A10	BZX84-A51
BZX79-C3V0	BZX83-C13	BZX84-A11	BZX84-A56
BZX79-C3V3	BZX83-C15	BZX84-A12	BZX84-A5V1
BZX79-C3V6	BZX83-C16	BZX84-A13	BZX84-A5V6
BZX79-C3V9	BZX83-C18	BZX84-A15	BZX84-A62
BZX79-C43	BZX83-C20	BZX84-A16	BZX84-A68
BZX79-C47	BZX83-C22	BZX84-A18	BZX84-A6V2
BZX79-C4V3	BZX83-C24	BZX84-A20	BZX84-A6V8
BZX79-C4V7	BZX83-C27	BZX84-A22	BZX84-A75
BZX79-C51	BZX83-C2V7	BZX84-A24	BZX84-A7V5
BZX79-C56	BZX83-C30	BZX84-A27	BZX84-A8V2
BZX79-C5V1	BZX83-C33	BZX84-A2V4	BZX84-A9V1
BZX79-C5V6	BZX83-C3V0	BZX84-A2V7	BZX84-B10
BZX79-C62	BZX83-C3V3	BZX84-A30	BZX84-B11
BZX79-C68	BZX83-C3V6	BZX84-A33	BZX84-B12
BZX79-C6V2	BZX83-C3V9	BZX84-A36	BZX84-B13
BZX79-C6V8	BZX83-C4V3	BZX84-A39	BZX84-B15

Multisim 14.1 Base Edition Components

BZX84-B16	BZX84B5V1LT1G	BZX84-C16	BZX84C4V7LT3G
BZX84B16LT1G	BZX84-B5V6	BZX84-C18	BZX84-C51
BZX84-B18	BZX84B5V6LT1G	BZX84-C20	BZX84-C56
BZX84-B20	BZX84-B62	BZX84-C22	BZX84-C5V1
BZX84-B22	BZX84-B68	BZX84-C24	BZX84C5V1LT1G
BZX84-B24	BZX84-B6V2	BZX84-C27	BZX84C5V1LT3G
BZX84-B27	BZX84B6V2LT1G	BZX84-C2V4	BZX84-C5V6
BZX84-B2V4	BZX84-B6V8	BZX84-C2V7	BZX84C5V6LT1G
BZX84-B2V7	BZX84B6V8LT1G	BZX84-C30	BZX84C5V6LT3G
BZX84-B30	BZX84-B75	BZX84-C33	BZX84-C62
BZX84-B33	BZX84-B7V5	BZX84C33LT1G	BZX84-C68
BZX84-B36	BZX84B7V5LT1G	BZX84C33LT3G	BZX84C68LT1G
BZX84-B39	BZX84-B8V2	BZX84-C36	BZX84-C6V2
BZX84-B3V0	BZX84B8V2LT1G	BZX84C36LT1G	BZX84C6V2LT1G
BZX84-B3V3	BZX84-B9V1	BZX84-C39	BZX84C6V2LT3G
BZX84-B3V6	BZX84B9V1LT1G	BZX84-C3V0	BZX84-C6V8
BZX84-B3V9	BZX84-C10	BZX84C3V0LT1G	BZX84C6V8LT1G
BZX84-B43	BZX84-C11	BZX84-C3V3	BZX84C6V8LT3G
BZX84-B47	BZX84-C12	BZX84-C3V6	BZX84-C75
BZX84-B4V3	BZX84C12LT1G	BZX84-C3V9	BZX84C75LT1G
BZX84-B4V7	BZX84-C13	BZX84-C43	BZX84-C7V5
BZX84B4V7LT1G	BZX84-C15	BZX84-C47	BZX84C7V5LT1G
BZX84-B51	BZX84C15LT1	BZX84-C4V3	BZX84-C8V2
BZX84-B56	BZX84C15LT1G	BZX84-C4V7	BZX84C8V2LT1G
BZX84-B5V1	BZX84C15LT3G	BZX84C4V7LT1G	BZX84-C9V1

Multisim 14.1 Base Edition Components

BZX84C9V1LT1G	BZX84J-B4V3	BZX84J-C2V4	BZX84J-C9V1
BZX84C9V1LT3G	BZX84J-B4V7	BZX84J-C2V7	BZX85-C10
BZX84J-B10	BZX84J-B51	BZX84J-C30	BZX85-C100
BZX84J-B11	BZX84J-B56	BZX84J-C33	BZX85-C11
BZX84J-B12	BZX84J-B5V1	BZX84J-C36	BZX85-C12
BZX84J-B13	BZX84J-B5V6	BZX84J-C39	BZX85-C13
BZX84J-B15	BZX84J-B62	BZX84J-C3V0	BZX85-C15
BZX84J-B16	BZX84J-B68	BZX84J-C3V3	BZX85-C16
BZX84J-B18	BZX84J-B6V2	BZX84J-C3V6	BZX85-C18
BZX84J-B20	BZX84J-B6V8	BZX84J-C3V9	BZX85-C20
BZX84J-B22	BZX84J-B75	BZX84J-C43	BZX85-C22
BZX84J-B24	BZX84J-B7V5	BZX84J-C47	BZX85-C24
BZX84J-B27	BZX84J-B8V2	BZX84J-C4V3	BZX85-C27
BZX84J-B2V4	BZX84J-B9V1	BZX84J-C4V7	BZX85-C30
BZX84J-B2V7	BZX84J-C10	BZX84J-C51	BZX85-C33
BZX84J-B30	BZX84J-C11	BZX84J-C56	BZX85-C36
BZX84J-B33	BZX84J-C12	BZX84J-C5V1	BZX85-C39
BZX84J-B36	BZX84J-C13	BZX84J-C5V6	BZX85-C3V3
BZX84J-B39	BZX84J-C15	BZX84J-C62	BZX85-C3V6
BZX84J-B3V0	BZX84J-C16	BZX84J-C68	BZX85-C3V9
BZX84J-B3V3	BZX84J-C18	BZX84J-C6V2	BZX85-C43
BZX84J-B3V6	BZX84J-C20	BZX84J-C6V8	BZX85-C47
BZX84J-B3V9	BZX84J-C22	BZX84J-C75	BZX85-C4V3
BZX84J-B43	BZX84J-C24	BZX84J-C7V5	BZX85-C4V7
BZX84J-B47	BZX84J-C27	BZX84J-C8V2	BZX85-C51

Multisim 14.1 Base Edition Components

BZX85-C56	BZX884-B2V7	BZX884-C10	BZX884-C68
BZX85-C5V1	BZX884-B30	BZX884-C11	BZX884-C6V2
BZX85-C5V6	BZX884-B33	BZX884-C12	BZX884-C75
BZX85-C62	BZX884-B36	BZX884-C13	BZX884-C7V5
BZX85-C68	BZX884-B39	BZX884-C16	BZX884-C8V2
BZX85-C6V2	BZX884-B3V0	BZX884-C20	BZX884-C9V1
BZX85-C6V8	BZX884-B3V3	BZX884-C22	C232A
BZX85-C75	BZX884-B3V6	BZX884-C24	C232B
BZX85-C7V5	BZX884-B3V9	BZX884-C2V4	C232D
BZX85-C82	BZX884-B43	BZX884-C2V7	C232F
BZX85-C8V2	BZX884-B47	BZX884-C30	C232M
BZX85-C91	BZX884-B4V3	BZX884-C33	C233A
BZX85-C9V1	BZX884-B4V7	BZX884-C36	C233B
BZX884-B10	BZX884-B51	BZX884-C3V0	C233D
BZX884-B11	BZX884-B56	BZX884-C3V3	C233F
BZX884-B12	BZX884-B5V1	BZX884-C3V6	C233M
BZX884-B13	BZX884-B5V6	BZX884-C3V9	CA0124E
BZX884-B15	BZX884-B62	BZX884-C43	CA0124M
BZX884-B16	BZX884-B68	BZX884-C47	CA0158AE
BZX884-B18	BZX884-B6V2	BZX884-C4V3	CA0158AT
BZX884-B20	BZX884-B6V8	BZX884-C4V7	CA0158E
BZX884-B22	BZX884-B75	BZX884-C51	CA0158M
BZX884-B24	BZX884-B7V5	BZX884-C56	CA0158T
BZX884-B27	BZX884-B8V2	BZX884-C5V1	CA0224E
BZX884-B2V4	BZX884-B9V1	BZX884-C62	CA0224M

Multisim 14.1 Base Edition Components

CA0258AE	CA3078AT	CA3140E	CA5160AE
CA0258AM	CA3078E	CA3140M	CA5160AM
CA0258AT	CA3078M	CA3140T	CA5260AE
CA0258E	CA3078T	CA3160E	CA5260AM
CA0258M	CA3080	CA3160T	CA5260E
CA0258T	CA3080A	CA3193AE	CA5260M
CA0324E	CA3080AE	CA3193AT	CA5420E
CA0324M	CA3080AM	CA3193E	CA5420M
CA0358AE	CA3080E	CA3193T	CA5420T
CA0358AM	CA3080M	CA3240AE	CA5470E
CA0358AT	CA3094AE	CA3240AE1	CA5470M
CA0358E	CA3094AM	CA3240E	CAP_ELECTROLIT_VIRTUAL
CA0358M	CA3094AT	CA3240E1	CAPACITOR_VIRTUAL
CA0358T	CA3094BE	CA3260E	CHIRP_CURRENT
CA0741E	CA3094BM	CA3260T	CHIRP_VOLTAGE
CA0741T	CA3094BT	CA3280E	
CA1458E	CA3094E	CA3440AE	CLC103AI
CA1458T	CA3094M	CA3440M	CLC103AM
CA2902M	CA3094T	CA3450E	CLC111AJE
CA2902N	CA3100E	CA5130AE	CLC111AJP
CA2904E	CA3100M	CA5130AM	CLC200A8C
CA2904M	CA3100T	CA5130AT	CLC200AI
CA3060E	CA3130E	CA5130E	CLC200AK
CA3078AE	CA3130M	CA5130M	CLC200AM
CA3078AM	CA3130T	CA5130T	CLC201

Multisim 14.1 Base Edition Components

CLC203	CLC405AIB	CLC412AJE	CLC423AJP
CLC220	CLC405AJE	CLC412AJP	CLC425A8B
CLC400A8B	CLC405AJP	CLC414A8B	CLC425AIB
CLC400A8D	CLC406A8B	CLC414A8D	CLC425AJE
CLC400AIB	CLC406A8D	CLC414AJE	CLC425AJP
CLC400AID	CLC406AJE	CLC414AJP	CLC426A8B
CLC400AJE	CLC406AJM5	CLC415A8B	CLC426AIB
CLC400AJP	CLC406AJP	CLC415A8D	CLC426AJE
CLC401A8B	CLC407AIB	CLC415AJE	CLC426AJP
CLC401A8D	CLC407AJE	CLC415AJP	CLC428A8B
CLC401AIB	CLC407AJP	CLC416AJE	CLC428AJE
CLC401AID	CLC409A8D	CLC416AJP	CLC428AJP
CLC401AJE	CLC409AID	CLC417AJE	CLC430A8B
CLC401AJP	CLC409AJE	CLC417AJP	CLC430AJE
CLC402A8B	CLC409AJM5	CLC420A8B	CLC430AJP
CLC402A8D	CLC409AJP	CLC420A8D	CLC431A8B
CLC402AID	CLC410A8B	CLC420AIB	CLC431AJE
CLC402AJE	CLC410A8D	CLC420AJE	CLC431AJP
CLC402AJP	CLC410AJE	CLC420AJP	CLC432A8B
CLC404A8D	CLC410AJP	CLC420B8B	CLC432AJE
CLC404AID	CLC411A8B	CLC420B8D	CLC432AJP
CLC404AJE	CLC411AJE	CLC420BIB	CLC440A8B
CLC404AJM5	CLC411AJP	CLC420BJE	CLC440AJE
CLC404AJP	CLC412A8B	CLC420BJP	CLC440AJP
CLC405A8B	CLC412AIB	CLC423AJE	CLC449A8B

Multisim 14.1 Base Edition Components

CLC449AJE	CNTR_4SDEC	CONTROL_3A	COUPLED_INDUCTORS
CLC449AJP	CNTR_7BIN	CONTROL_3C	CPH3105-TL-E
CLC501A8D	CNTR_8SBIN	CONTROL_4A	CPH3122-TL-E
CLC501AID	CNTR_BCD_S	CONTROL_4C	CPH3123-TL-E
CLC501AJE	CNTR_BCD_SDC	CONTROL_NC	CPH3144-TL-E
CLC501AJP	CNTR_BCD_SU_D	CONTROL_NO	CPH3145-TL-E
CLC502A8D	CNTR_BIN_DEC_SU_D	CONTROLLED_ONE_SHOT	CPH3205-TL-E
CLC502AID	CNTR_JOHNSON	COP87L20CJN	CPH3223-TL-E
CLC502AJE	CNY17F-3	COP87L22CJN	CPH3448-TL-H
CLC502AJP	CNY17F-3X001	COP87L40CJN	CPH3910-TL-E
CLC505A8D	CNY17F-3X006	COP87L40RJN	CPH5505-TL-E
CLC505AJE	CNY17F-3X007T	COP87L42CJN	CPH5506-TL-E
CLC505AJP	CNY17F-3X009T	COP87L42RJN	CPH5617-TL-E
CLOCK_CURRENT	CNY17F-3X016	CORELESS_COIL_VIRTUAL	CPH5905G-TL-E
CLOCK_VOLTAGE	CNY17F-3X017	COUNT_OFF	CPH6223-TL-E
CM1213A-02SR	CNY17F-3X019	COUNT_OFF_HOLD	CPH6341-TL-E
CNTR_16SBIN	COMP_4	COUNT_OFF_RESET	CPH6445-TL-E
CNTR_4ABIN	COMPARATOR_IDEAL	COUNT_ON	CPH6531-TL-E
CNTR_4ADEC	COMPARATOR_VIRTUAL	COUNT_ON_HOLD	CRYSTAL_VIRTUAL
CNTR_4BIN_AS	CONTROL_1A	COUNT_ON_RESET	CS494001-LQFP(144)
CNTR_4BIN_ASCLR	CONTROL_1C	COUNT_UPDOWN_OFF	CS494501-TQFP(100)
CNTR_4BIN_S	CONTROL_2A	COUNT_UPDOWN_ON	CURRENT_CONTROLLED_CURRENT_SOURCE
CNTR_4BIN_SU_D	CONTROL_2C		
CNTR_4BINS_DC			
CNTR_4SBIN			

Multisim 14.1 Base Edition Components

CURRENT_CONTROLLED_SPST	D_LATCH_NEGSR	DCC010-TB-E	DELAY
	D1N4148	DCD_2TO4	DEM4_16
CURRENT_CONTROLLED_SPST_ANIMATED	D44C12G	DCD_3TO8	DF06MA-E3/45
	D44H11G	DCD_4TO16	DF10S/45
CURRENT_CONTROLLED_VOLTAGE_SOURCE	D44H8G	DCD_7SEG	DF10SA-E3/45
	D44VH10G	DCD_7SEG_P	DF1510S-E3/77
CURRENT_LIMITER_BLOCK	D45C12G	DCD_BARGRAPH	DF3A6.8FUT1G
	D45H11G	DCD_HEX	DF6A6.8FUT1G
CY37032P44-125AC	D45H8G	DCD_HEX_BLUE	DGND
CY37032P44-125AI	D45VH10G	DCD_HEX_DIG_BLUE	DIGITAL_CLOCK
CY37032P44-125JC	DAC7642_FP32	DCD_HEX_DIG_GREEN	DIGITAL_CONSTANT
CY37032P44-125JI	DAC7643_FP32		
CY37032P44-154AC	DAC8541	DCD_HEX_DIG_ORANGE	DIGITAL_FREQUENCY_DIVIDER
CY37032P44-154AI	DAN222M3T5G		DIGITAL_HIGH
CY37032P44-154JC	DAP222M3T5G	DCD_HEX_DIG_RED	DIGITAL_LOW
CY37032P44-154JI	DBREAK	DCD_HEX_DIG_YELLOW	DIGITAL_PULLDOWN
CY37032P44-200AC	DC_CURRENT	DCD_HEX_GREEN	DIGITAL_PULLUP
CY37032P44-200JC	DC_INTERACTIVE_CURRENT	DCD_HEX_ORANGE	DIGITAL_STATE_MACHINE
CY37032P44-222AC	DC_INTERACTIVE_VOLTAGE	DCD_HEX_YELLOW	
CYPRESS-ULTRA-ISR-HDR	DC_MACHINE_PERMANENT_MAGNET	DEC_BCD_10_INV	DIODE
		DEC_BCD_7	DIODE
D_FF	DC_MACHINE_WOUND_FIELD	DEC2_4	DIP10
D_FF_NEGSR		DEC3_8	DIP12
D_FF_POSSR	DC_POWER	DEC4_10	DIP14
D_LATCH			

Multisim 14.1 Base Edition Components

DIP16	DPDT_SB	DSUB25F	DTA115TET1G
DIP18	DPST_2NC_DB	DSUB25M	DTA115TM3T5G
DIP20	DPST_2NC_SB	DSUB37F	DTA123EM3T5G
DIP22	DPST_2NO_DB	DSUB37M	DTA123TET1G
DIP24	DPST_2NO_SB	DSUB9F	DTA123TM3T5G
DIP28	DS1846_SO20	DSUB9M	DTA124EET1G
DIP4	DS80C310_LCC44	DSWPK_10	DTA124EM3T5G
DIP6	DS80C320_LCC44	DSWPK_2	DTA124XM3T5G
DIP8	DS80C323_LCC44	DSWPK_3	DTA143EET1G
DIPSW1	DS83C520_LCC44	DSWPK_4	DTA143EM3T5G
DIPSW10	DS83C530_FP52	DSWPK_5	DTA143ZET1G
DIPSW2	DS87C520_LCC44	DSWPK_6	DTA143ZM3T5G
DIPSW3	DS87C530_FP52	DSWPK_7	DTA144EET1G
DIPSW4	DSL70	DSWPK_8	DTA144EM3T5G
DIPSW5	DSP16210- TQFP(144)	DSWPK_9	DTA144TET1G
DIPSW6		DTA113EET1G	DTA144TM3T5G
DIPSW7	DSP1628- BQFP(100)	DTA113EM3T5G	DTA144WM3T5G
DIPSW8	DSP1628- TQFP(100)	DTA114EET1G	DTC113EET1G
DIPSW9		DTA114EM3T5G	DTC113EM3T5G
DIV	DSP16410B- PBGA(208)	DTA114TET1G	DTC114EET1G
DIVIDER		DTA114TM3T5G	DTC114EM3T5G
DP8421A	DSUB15F	DTA114YET1G	DTC114TET1G
DP8421A_LCC68	DSUB15F-VGA	DTA114YM3T5G	DTC114TM3T5G
DP8422A_LCC84	DSUB15M	DTA115EET1G	DTC114YET1G
	DSUB15M-VGA	DTA115EM3T5G	DTC115EET1G
DPDT_DB			

Multisim 14.1 Base Edition Components

DTC115EM3T5G	ECG6412	EL2006G	EL4430CN
DTC115TET1G	ECH8102-TL-H	EL2006G/883B	EL4430CS
DTC115TM3T5G	ECH8649-TL-H	EL2022/EL	EL4451CN
DTC123EM3T5G	ECH8651R-R-TL-H	EL2022CG	EL4451CS
DTC123JET1G	ECH8651R-TL-H	EL2022G	EL4452CN
DTC123JM3T5G	ECH8652-TL-H	EL2157CN	EL4452CS
DTC123TET1G	ECH8653-TL-H	EL2157CS	ELH0032G/883B
DTC123TM3T5G	ECH8654-TL-H	EL2210CN	ELH0101K/883B
DTC124EET1G	ECH8657-TL-H	EL2210CS	EMC2DXV5T1G
DTC124EM3T5G	ECH8660-TL-H	EL2211CN	EMC3DXV5T1G
DTC124XET1G	ECH8662-TL-H	EL2211CS	EMC3DXV5T5G
DTC124XM3T5G	EDF1DS-E3/45	EL2310CN	EMC4DXV5T1G
DTC143EET1G	EDR201A05	EL2310CS	EMC5DXV5T1G
DTC143EM3T5G	EDR201A12	EL2311CN	EMH1303-TL-E
DTC143TM3T5G	EDR201A24	EL2311CS	EMH1405-TL-H
DTC143ZET1G	EDR2H1A05	EL2410CN	EMR011A03
DTC143ZM3T5G	EDR2H1A12	EL2410CS	EMR011A05
DTC144EET1G	EDR2H1A24	EL2411CN	EMR011A06
DTC144EM3T5G	EGF1D-E3/67A	EL2411CS	EMR011A08
DTC144TET1G	EGF1T-E3/67A	EL2500/EL	EMR011A09
DTC144TM3T5G	EGP10D-E3/54	EL2520/EL	EMR011A12
DTC144WM3T5G	EGP10G-E3/54	EL2600/EL	EMR011A24
ECG6407	EGP50D-E3/54	EL2620/EL	EMR011B03
ECG6408	EGP50G-E3/54	EL4089CN	EMR011B05
ECG6411	EL2006CG	EL4089CS	EMR011B06

Multisim 14.1 Base Edition Components

EMR011B08	EMR031B03	EMR131A09	EMR171A06
EMR011B09	EMR031B05	EMR131A12	EMR171A08
EMR011B12	EMR031B06	EMR131A24	EMR171A09
EMR011B24	EMR031B08	EMR131B03	EMR171A12
EMR021A03	EMR031B09	EMR131B05	EMR171A24
EMR021A05	EMR031B12	EMR131B06	EMX1DXV6T1G
EMR021A06	EMR031B24	EMR131B08	EMX1DXV6T5G
EMR021A08	EMR121A03	EMR131B09	EN2016CM
EMR021A09	EMR121A05	EMR131B12	EN2016CN
EMR021A12	EMR121A06	EMR131B24	ENC_10TO4
EMR021A24	EMR121A08	EMR151A03	ENC_8TO3
EMR021B03	EMR121A09	EMR151A05	ENC_8TO3S
EMR021B05	EMR121A12	EMR151A06	ENC10_4
EMR021B06	EMR121A24	EMR151A08	ENC8_3
EMR021B08	EMR121B03	EMR151A09	ENERGIZING_COIL
EMR021B09	EMR121B05	EMR151A12	ENERGIZING_COIL_ AC
EMR021B12	EMR121B06	EMR151A24	ENERGIZING_COIL_ TIMED
EMR021B24	EMR121B08	EMR161A03	
EMR031A03	EMR121B09	EMR161A05	EP2015ACN
EMR031A05	EMR121B12	EMR161A06	EP2015CM
EMR031A06	EMR121B24	EMR161A08	EP2015CN
EMR031A08	EMR131A03	EMR161A09	EPM7032-PLCC(44)
EMR031A09	EMR131A05	EMR161A12	EPM7032-PQFP(44)
EMR031A12	EMR131A06	EMR171A03	EPM7032S- PLCC(44)
EMR031A24	EMR131A08	EMR171A05	

Multisim 14.1 Base Edition Components

EPM7032S-TQFP(44)	EPM7128A-TQFP(100)	ESD105-B1-02ELS	ESD206-B1-02V
EPM7032-TQFP(44)	EPM7128A-TQFP(144)	ESD108-B1-CSP0201	ESD207-B1-02EL
EPM7064-PLCC(44)	EPM7512AE-PQFP(208)	ESD110-B1-02EL	ESD207-B1-02ELS
EPM7064-PLCC(68)	EPM7512AE-TQFP(144)	ESD110-B1-02ELS	ESD208-B1-02EL
EPM7064-PLCC(84)	ES1B-E3/61T	ESD112-B1-02EL	ESD208-B1-02ELS
EPM7064-PQFP(100)	ES1C-E3/61T	ESD112-B1-02ELS	ESD217-B1-02EL
EPM7064S-PLCC(44)	ES1D-E3/61T	ESD113-B1-02EL	ESD218-B1-02ELS
EPM7064S-PLCC(84)	ES1PD-E3/84A	ESD113-B1-02ELS	ESD221-U1-02EL
EPM7064S-TQFP(100)	ES2B-E3/52T	ESD119-B1-W01005	ESD24VS2U
EPM7064S-TQFP(44)	ES2C-E3/52T	ESD11L5.0DT5G	ESD300-B1-02LRH
EPM7064-TQFP(44)	ES2D-E3/52T	ESD129-B1-W01005	ESD307-U1-02N
EPM7064-TQFP(44)	ES3D-E3/57T	ESD18VU1B-02LRH	ESD311-U1-02N
EPM7096-PLCC(68)	ESD0P2RF-02LRH	ESD18VU1B-02LS	ESD3V3U4ULC
EPM7096-PLCC(84)	ESD101-B1-02EL	ESD200-B1-CSP0201	ESD5004MXTBG
EPM7096-PQFP(100)	ESD101-B1-02ELS	ESD202-B1-CSP01005	ESD5371MXT5G
EPM7128AE-PLCC(84)	ESD102-U1-02ELS	ESD203-B1-02EL	ESD5581MXT5G
EPM7128AE-TQFP(100)	ESD102-U2-099EL	ESD203-B1-02ELS	ESD5B5.0ST1G
EPM7128AE-TQFP(144)	ESD102-U4-05L	ESD204-B1-02EL	ESD5V3L1B-02LS
EPM7128A-PLCC(84)	ESD103-B1-02EL	ESD204-B1-02ELS	ESD5V3L1U-02LRH
	ESD103-B1-02ELS	ESD205-B1-02EL	ESD5V3U2U-03F
	ESD105-B1-02EL	ESD205-B1-02ELS	ESD5V3U2U-03LRH
		ESD206-B1-02EL	ESD5V3U4RRS
		ESD206-B1-02ELS	ESD5V3U4U-HDMI
			ESD5V5U5ULC
			ESD5Z12T1G

Multisim 14.1 Base Edition Components

ESD5Z2.5T1G	ESD9X12ST5G	FCX558	FMMD6050
ESD5Z3.3T1G	ESD9X3.3ST5G	FCX649	FMMD6100
ESD5Z5.0T1G	ESD9X5.0ST5G	FCX749	FMMD7000
ESD5Z6.0T1G	ESDR0502NMUTAG	FEP16DT-E3/45	FMMD914
ESD5Z7.0T1G	ESDR0502NMUTBG	FEP30GP-E3/45	FMMT38B
ESD5Z7.0T5G	ESDR0544MDMR4G	FEP30JPE3/45	FMMT489
ESD7004MUTAG	ESH1PD-E3/84A	FES16BT-E3/45	FMMT491A
ESD7008MUTAG	EVAL-SDP-CB1Z	FES16GT-E3/45	FMMT5179
ESD7016MUTAG	EVAL-SDP-CH1Z	FES8DT-E3/45	FMMT549
ESD7104MUTAG	EVAL-SDP-CH1Z_FMC	FF_D_CO	FMMT589
ESD7181MUT5G	EVAL-SDP-CS1Z	FF_D_PCLR_CO	FMMT591A
ESD7462N2T5G	EXPONENTIAL_CURRENT	FF_D4_CLR_CO	FMMT597
ESD7951ST5G	EXPONENTIAL_VOLTAGE	FF_JK_NSCLR_CO	FMMT597Q
ESD7C3.3DT5G	EXPONENTIAL_VOLTAGE	FF_JK_PSCLR_CO	FMMT617
ESD7C5.0DT5G	F1007	FF_T_CLR_CO	FMMT618
ESD8004MUTAG	F1008	FLOAT_NC	FMMT619
ESD8011MUT5G	F1020	FLOAT_NO	FMMT624
ESD8040MUTAG	FAST_1A	FLOW_NC	FMMT625
ESD8V0R1B-02EL	FAST_2A	FLOW_NO	FMMT717
ESD8V0R1B-02ELS	FAST_3A	FM_CURRENT	FMMT718
ESD9B3.3ST5G	FAST_4A	FM_VOLTAGE	FMMT720
ESD9B5.0ST5G	FCN-268D024-G/10-R	FMMD2835	FMMT722
ESD9C3.3ST5G	FCX458	FMMD2836	FMMT723
ESD9C5.0ST5G		FMMD2837	FMMT918
ESD9L5.0ST5G		FMMD2838	FMMTA20

Multisim 14.1 Base Edition Components

FMMTA70	FX8-120S-SV(21)	GaAsFET_P	GI816
FMMTH10	FZT604	GAIN_2_PIN	GI817
FMMV105G	FZT605	GBPC3506W-E4/51	GI818
FMMV109	FZT649	GBU4G-E3/45	GL34A
FMMV2101	FZT651	GBU4M-E3/51	GL34B
FMMV2102	FZT657	GBU6G-E3/45	GL34D
FMMV2103	FZT658	GBU6M-E3/45	GL34G
FMMV2104	FZT688B	GEN_CNTR_4ABIN	GL34G-E3/98
FMMV2105	FZT689B	GF1A	GL34J
FMMV2106	FZT690B	GF1B	GLL4735
FMMV2107	FZT692B	GF1D	GLL4736
FMMV2108	FZT694B	GF1G	GLL4737
FMMV2109	FZT696B	GF1G-E3/67A	GLL4738
FMMV3102	FZT705	GF1J	GLL4739
FOOT_NC	FZT749	GF1K	GLL4740
FOOT_NO	FZT751	GF1M	GLL4741
FREQ_DIVIDER	FZT757	GI250-1	GLL4742
FREQUENCY_TABLE _FUNCTION	FZT758	GI250-2	GLL4743
	FZT788A	GI250-3	GLL4744
FSK_VOLTAGE	FZT788B	GI250-4	GLL4745
FULL_ADDER	FZT789A	GI751-E3/54	GLL4746
FUSE	FZT790A	GI810	GLL4747
FUSE_VIRTUAL	FZT792A	GI811	GLL4748
FX2-100S- 1.27DS(71)	G3SBA60-E3/51	GI812	GLL4749
FX8-120P-SV1(91)	GaAsFET_N	GI814	GLL4750

Multisim 14.1 Base Edition Components

GLL4751	GP10B	GP30A	HA1-2542-5
GLL4752	GP10D	GP30B	HA1-2839-5
GLL4753	GP10G	GP30D	HA1-2840-5
GLL4754	GP10J	GP30G	HA1-2840-9
GLL4755	GP10K	GP30J	HA1-2850-5
GLL4756	GP10M	GP30K	HA1-2850-9
GLL4757	GP10N	GP30M	HA1-4741-2
GLL4758	GP10Q	GROUND	HA1-4741-5
GLL4759	GP10T	GROUND_REF1	HA1-5104-2
GLL4760	GP10V	GROUND_REF2	HA1-5104-5
GLL4761	GP10W	GROUND_REF3	HA1-5114-2
GLL4762	GP10Y	GROUND_REF4	HA1-5114-5
GLL4763	GP10Y-E3/54	GROUND_REF5	HA1-5134-2
GP02-20	GP15A	GSB311A41EU	HA1-5134-5
GP02-25	GP15B	GSB3211311WEU	HA1-5190-2
GP02-30	GP15D	GSIB1580-E3/45	HA2-2500-2
GP02-35	GP15G	GSIB2560-E3/45	HA2-2502-2
GP02-40	GP15J	GTO	HA2-2510-2
GP02-40-E3/54	GP15K	HA1-2539-2	HA2-2512-2
GP08A	GP15M	HA1-2539-5	HA2-2515-2
GP08B	GP20A	HA1-2540-2	HA2-2520-2
GP08D	GP20B	HA1-2540-5	HA2-2522-2
GP08G	GP20D	HA1-2541-2	HA2-2525-5
GP08J	GP20G	HA1-2541-5	HA2-2529-2
GP10A	GP20J	HA1-2542-2	HA2-2529-5

Multisim 14.1 Base Edition Components

HA2-2541-2	HA2-5162-5	HA3-2840-9	HA3-7712B-5
HA2-2541-5	HA2-5170-2	HA3-2841-5	HA3-7712B-9
HA2-2542-2	HA2-5170-5	HA3-2841-9	HA3B2840-5
HA2-2542-5	HA2-5190-2	HA3-2842-5	HA3B2840-9
HA2-2544-2	HA2-5221-5	HA3-2842-9	HA3B2841-5
HA2-2548-5	HA2-7712A-5	HA3-2850-5	HA3B2841-9
HA2-2548-9	HA2-7712A-9	HA3-2850-9	HA3B2842-5
HA2-2600-2	HA2-7712B-5	HA3-4741-5	HA3B2842-9
HA2-2602-2	HA2-7712B-9	HA3-5101-5	HA3B2850-5
HA2-2605-5	HA3-2444-5	HA3-5102-5	HA3B2850-9
HA2-2620-2	HA3-2444-9	HA3-5104-5	HA4P2525-5
HA2-2622-2	HA3-2525-5	HA3-5111-5	HA7-2500-2
HA2-2625-5	HA3-2529-5	HA3-5112-5	HA7-2510-2
HA2-2640-2	HA3-2539-5	HA3-5114-5	HA7-2512-2
HA2-5101-2	HA3-2539C-5	HA3-5127-5	HA7-2515-2
HA2-5102-2	HA3-2540-5	HA3-5127A-5	HA7-2520-2
HA2-5102-5	HA3-2542-5	HA3-5142-5	HA7-2522-2
HA2-5130-5	HA3-2544-5	HA3-5147-5	HA7-2525-5
HA2-5135-5	HA3-2544C-5	HA3-5177-5	HA7-2529-5
HA2-5142-2	HA3-2548-5	HA3-5221-5	HA7-2544-2
HA2-5142-5	HA3-2605-5	HA3-5222-5	HA7-2544-5
HA2-5147-2	HA3-2625-5	HA3-5232-5	HA7-2548-5
HA2-5147-5	HA3-2839-5	HA3-5232-9	HA7-2600-2
HA2-5160-2	HA3-2839-9	HA3-7712A-5	HA7-2602-2
HA2-5160-5	HA3-2840-5	HA3-7712A-9	HA7-2605-5

Multisim 14.1 Base Edition Components

HA7-2620-2	HA7-5142-5	HA9P2841-5	HA9P5232-5
HA7-2622-2	HA7-5147-2	HA9P2841-9	HA9P5232-9
HA7-2625-5	HA7-5147-5	HA9P2842-5	HA9P7712B-5
HA7-2640-2	HA7-5170-2	HA9P2842-9	HA9P7712B-9
HA7-2645-5	HA7-5170-5	HA9P2850-5	HALF_ADDER
HA7-2840-5	HA7-5177-5	HA9P2850-9	HC-49/U_1.5MHz
HA7-2840-9	HA7-5221-5	HA9P4741-9	HC-49/U_11MHz
HA7-2850-5	HA7-5221-9	HA9P5101-5	HC-49/U_15MHz
HA7-2850-9	HA7-5222-5	HA9P5101-9	HC-49/U_25MHz
HA7-5101-2	HA7-5222-9	HA9P5102-5	HC-49/U_3MHz
HA7-5102-2	HA9P2444-5	HA9P5102-9	HC-49/U_40MHz
HA7-5102-5	HA9P2444-9	HA9P5104-5	HC-49/U_5MHz
HA7-5111-2	HA9P2529-5	HA9P5104-9	HC-49/U_7MHz
HA7-5112-2	HA9P2539-5	HA9P5111-5	HC-49/U_80MHz
HA7-5127-2	HA9P2539-9	HA9P5111-9	HC-49/US_11MHz
HA7-5127-5	HA9P2540-5	HA9P5112-5	HC-49/US_15MHz
HA7-5127A-2	HA9P2544-5	HA9P5112-9	HC-49/US_25MHz
HA7-5127A-5	HA9P2544-9	HA9P5114-5	HC-49/US_40MHz
HA7-5130-2	HA9P2544C-5	HA9P5114-9	HC-49/US_5MHz
HA7-5130-5	HA9P2544C-9	HA9P5127-5	HC-49/US_7MHz
HA7-5135-2	HA9P2548-5	HA9P5137-5	HCNR200-000E
HA7-5135-5	HA9P2605-5	HA9P5142-9	HCNR200-050E
HA7-5137-2	HA9P2625-5	HA9P5221-5	HCNR200-300E
HA7-5137-5	HA9P2840-5	HA9P5222-5	HCNR200-350E
HA7-5142-2	HA9P2840-9	HA9P5222-9	HCNW136-000E

Multisim 14.1 Base Edition Components

HCNW136-300E	HCPL-181-000E	HCPL-2231-300E	HCPL-4504-320E
HCNW139-000E	HCPL-181-060E	HCPL-2232-000E	HCPL-4504-360E
HCNW139-300E	HCPL-2200-000E	HCPL-2232-300E	HCPL-4506-000E
HCNW2201-000E	HCPL-2200-300E	HCPL-263L-000E	HCPL-4506-020E
HCNW2201-300E	HCPL-2201-000E	HCPL-263L-020E	HCPL-4506-060E
HCNW3120-000E	HCPL-2201-060E	HCPL-263L-060E	HCPL-4506-300E
HCNW3120-300E	HCPL-2201-300E	HCPL-263L-300E	HCPL-4506-320E
HCPL-0201-000E	HCPL-2201-360E	HCPL-263L-320E	HCPL-4506-360E
HCPL-0201-060E	HCPL-2202-000E	HCPL-263L-560E	HCPL-7510-000E
HCPL-0211-000E	HCPL-2202-060E	HCPL-3020-000E	HCPL-7510-060E
HCPL-0211-060E	HCPL-2202-300E	HCPL-3020-060E	HCPL-7510-300E
HCPL-0302-000E	HCPL-2202-360E	HCPL-3020-300E	HCPL-7510-360E
HCPL-0302-060E	HCPL-2211-000E	HCPL-3120-000E	HCPL-7800-000E
HCPL-0314-000E	HCPL-2211-060E	HCPL-3120-060E	HCPL-7800-300E
HCPL-0314-060E	HCPL-2211-300E	HCPL-3120-300E	HCPL-J312-000E
HCPL-0454-000E	HCPL-2211-360E	HCPL-3120-360E	HCPL-J312-300E
HCPL-0454-060E	HCPL-2212-000E	HCPL-3140-000E	HD4A
HCPL-0466-000E	HCPL-2212-060E	HCPL-3140-060E	HD64F2134FA20
HCPL-0466-060E	HCPL-2212-300E	HCPL-3140-300E	HD64F2134TF20
HCPL-0501-500E	HCPL-2212-360E	HCPL-3140-360E	HD64F2134VFA10
HCPL-0501-560E	HCPL-2219-000E	HCPL-316J-000E	HD64F2134VTF10
HCPL-063L-000E	HCPL-2219-060E	HCPL-4504-000E	HDR1X10
HCPL-063L-060E	HCPL-2219-300E	HCPL-4504-020E	HDR1X11
HCPL-0701-000E	HCPL-2219-360E	HCPL-4504-060E	HDR1X12
HCPL-0701-060E	HCPL-2231-000E	HCPL-4504-300E	HDR1X13

Multisim 14.1 Base Edition Components

HDR1X14	HDR2X15	HFA2-0002-9	HSDL-5420#031
HDR1X15	HDR2X16	HFA2-0005-5	HSP43124PC-33
HDR1X16	HDR2X17	HFA2-0005-9	HSP43124PC-45
HDR1X17	HDR2X18	HFA3-0001-5	HSP43168GM-25/883
HDR1X18	HDR2X19	HFA3-0001-9	HSP43168GM-33/883
HDR1X19	HDR2X2	HFA3-0002-5	HSP45240GM-25/883
HDR1X2	HDR2X20	HFA3-0002-9	HSP45240GM-33/883
HDR1X20	HDR2X21	HFA3-0005-5	HSP45240GM-40/883
HDR1X21	HDR2X22	HFA3-0005-9	ICL7611ACPA
HDR1X22	HDR2X23	HFA7-0002-5	ICL7611ACTV
HDR1X23	HDR2X24	HFA7-0002-9	ICL7611AMTV
HDR1X24	HDR2X25	HFA7-0005-5	ICL7611DCBA
HDR1X25	HDR2X3	HFA7-0005-9	ICL7650SCBA-1
HDR1X3	HDR2X4	HFA9P0001-5	ICL7650SCBD
HDR1X4	HDR2X5	HFA9P0002-5	ICL7650SCPA
HDR1X5	HDR2X6	HFA9P0002-9	ICL7650SCPD
HDR1X6	HDR2X7	HFA9P0005-5	ICL7650SCTV-1
HDR1X7	HDR2X8	HFA9P0005-9	ICL7650SIJD
HDR1X8	HDR2X9	HMA510GM-55/833	ICL7650SIPA-1
HDR1X9	HELD_CLOSED_LIMIT	HMA510GM-65/833	ICL7650SIPD
HDR2X10	HELD_OPEN_LIMIT	HMA510GM-75/833	ICL7650SITV-1
HDR2X11	HFA1-0001-5	HSDL-5400	ICL7650SMJD
HDR2X12	HFA1-0001-9	HSDL-5420	
HDR2X13	HFA2-0002-5		
HDR2X14			

Multisim 14.1 Base Edition Components

ICL7650SMTV-1	IDT7210L35F	INA148UA	INA202AID
ICL7652	IDT7210L35G	INA152EA/250	INA202AIDGKR
ICL7652D	IDT7210L35J	INA154U	INA203AID
ICL7652P	IDT7210L45C	INA154UA	INA203AIPW
ICM7555ESA+	IDT7210L45F	INA157U	INA206AID
ICM7555IJA+	IDT7210L45G	INA157UA	INA206AIPW
ICM7555IPA+	IDT7210L45J	INA159AID	INA210AIDCKR
ICM7555ISA+	IDT7210L55C	INA163UA	INA210AIRSWR
ICM7555ITV	IDT7210L55F	INA168NA	INA210BIDCKR
ICM7555MJA	IDT7210L55G	INA169NA	INA210BIRSWR
ICM7555MTV	IDT7210L55J	INA170EA	INA211AIDCKR
ICM7556IPD+	IDT7210L65C	INA188ID	INA211BIDCKR
ICM7556ISD+	IDT7210L65F	INA193AID	INA2126E/250
ICM7556MJD+	IDT7210L65G	INA194AID	INA2126EA/250
IDAC	IDT7210L65J	INA195AID	INA2126P
IDAC16	ILLUMINATED_PB	INA199A1DCKR	INA2126U
IDT7210L20C	IMSA110-G20S	INA199A1RSWR	INA212AIDCKR
IDT7210L20F	INA105_CMP	INA199A2DCKR	INA212BIDCKR
IDT7210L20G	INA133U	INA199A2RSWR	INA2132U
IDT7210L20J	INA133UA	INA199A3DCKR	INA2132UA
IDT7210L25C	INA138NA	INA199A3RSWR	INA213AIDCKR
IDT7210L25F	INA143U	INA200AID	INA213AIDCKT
IDT7210L25G	INA143UA	INA200AIDGKR	INA213AIRSWR
IDT7210L25J	INA145UA	INA201AID	INA213BIDCKR
IDT7210L35C	INA146UA	INA201AIDGKR	INA213BIRSWR

Multisim 14.1 Base Edition Components

INA214AIDCKR	INDUCTOR_ADVANCED	IPB014N06N	IPB037N06N3 G
INA214AIRSWR	Inductor_Lossy	IPB015N04L G	IPB038N12N3 G
INA214BIDCKR	INDUCTOR_VIRTUAL	IPB015N04N G	IPB039N04L G
INA214BIRSWR		IPB016N06L3 G	IPB039N10N3 G
INA215AIDCKR	INTERACTIVE_DIGITAL_CONSTANT	IPB017N06N3 G	IPB041N04N G
INA216A2RSWR		IPB019N06L3 G	IPB042N03L G
INA216A2YFFR	INV	IPB019N08N3 G	IPB042N10N3 G
INA216A3RSWR	IPA028N08N3 G	IPB020N04N G	IPB048N06L G
INA216A3YFFR	IPA030N10N3 G	IPB020NE7N3 G	IPB049N06L3 G
INA216A4RSWR	IPA032N06N3 G	IPB021N06N3 G	IPB049NE7N3 G
INA216A4YFFR	IPA037N08N3 G	IPB022N04L G	IPB050N06N G
INA225AIDGKR	IPA045N10N3 G	IPB023N04N G	IPB052N04N G
INA270AID	IPA057N06N3 G	IPB023N06N3 G	IPB054N06N3 G
INA271AID	IPA057N08N3 G	IPB025N08N3 G	IPB054N08N3 G
INA300AIDSQR	IPA075N15N3 G	IPB025N10N3 G	IPB055N03L G
INA321E	IPA086N10N3 G	IPB026N06N	IPB057N06N
INA321EA	IPA093N06N3 G	IPB027N10N3 G	IPB065N03L G
INA322EA	IPA100N08N3 G	IPB029N06N3 G	IPB065N15N3 G
INA326EA	IPA105N15N3 G	IPB030N08N3 G	IPB067N08N3 G
INA327EA	IPA126N10N3 G	IPB031NE7N3 G	IPB072N15N3 G
INA331AIDGK	IPA180N10N3 G	IPB034N03L G	IPB075N04L G
INA331IDGK	IPB009N03L G	IPB034N06L3 G	IPB080N03L G
INA332IDGK	IPB010N06N	IPB034N06N3 G	IPB081N06L3 G
INA333AIDGKR	IPB011N04L G	IPB035N08N3 G	IPB083N10N3 G
INA333AIDRGR	IPB011N04N G	IPB036N12N3 G	IPB090N06N3 G

Multisim 14.1 Base Edition Components

IPB093N04L G	IPD035N06L3 G	IPD127N06L G	IPI028N08N3 G
IPB096N03L G	IPD036N04L G	IPD12CN10N G	IPI029N06N
IPB097N08N3 G	IPD038N04N G	IPD135N03L G	IPI030N10N3 G
IPB107N20N3 G	IPD038N06N3 G	IPD135N08N3 G	IPI032N06N3 G
IPB107N20NA	IPD040N03L G	IPD144N06N G	IPI034NE7N3 G
IPB108N15N3 G	IPD042P03L3 G	IPD160N04L G	IPI037N06L3 G
IPB114N03L G	IPD048N06L3 G	IPD170N04N G	IPI037N08N3 G
IPB123N10N3 G	IPD050N03L G	IPD180N10N3 G	IPI040N06N3 G
IPB136N08N3 G	IPD053N06N	IPD200N15N3 G	IPI041N12N3 G
IPB144N12N3 G	IPD053N06N3 G	IPD220N06L3 G	IPI045N10N3 G
IPB147N03L G	IPD053N08N3 G	IPD230N06N G	IPI04CN10N G
IPB200N15N3 G	IPD060N03L G	IPD250N06N3 G	IPI052NE7N3 G
IPB200N25N3 G	IPD068N10N3 G	IPD25CN10N G	IPI057N08N3 G
IPB230N06L3 G	IPD068P03L3 G	IPD320N20N3 G	IPI070N08N3 G
IPB260N06N3 G	IPD075N03L G	IPD33CN10N G	IPI072N10N3 G
IPB26CN10N G	IPD079N06L3 G	IPD350N06L G	IPI075N15N3 G
IPB320N20N3 G	IPD082N10N3 G	IPD400N06N G	IPI076N12N3 G
IPB34CN10N G	IPD088N04L G	IPD530N15N3 G	IPI084N06L3 G
IPB50CN10N G	IPD088N06N3 G	IPD600N25N3 G	IPI086N10N3 G
IPB530N15N3 G	IPD090N03L G	IPD640N06L G	IPI100N08N3 G
IPB600N25N3 G	IPD096N08N3 G	IPD78CN10N G	IPI110N20N3 G
IPD025N06N	IPD105N03L G	IPD800N06N G	IPI111N15N3 G
IPD031N03L G	IPD105N04L G	IPI020N06N	IPI126N10N3 G
IPD031N06L3 G	IPD110N12N3 G	IPI023NE7N3 G	IPI139N08N3 G
IPD034N06N3 G	IPD122N10N3 G	IPI024N06N3 G	IPI147N12N3 G

Multisim 14.1 Base Edition Components

IPI180N10N3 G	IPP040N06N3 G	IPP086N10N3 G	IPP50CN10N G
IPI200N15N3 G	IPP041N04N G	IPP08CN10L G	IPP530N15N3 G
IPI200N25N3 G	IPP041N12N3 G	IPP093N06N3 G	IPP600N25N3 G
IPI26CN10N G	IPP042N03L G	IPP096N03L G	IPP80CN10N G
IPI320N20N3 G	IPP045N10N3 G	IPP100N08N3 G	IPS031N03L G
IPI35CN10N G	IPP048N12N3 G	IPP110N20N3 G	IPS040N03L G
IPI50CN10N G	IPP04CN10N G	IPP110N20NA	IPS050N03L G
IPI530N15N3 G	IPP052N06L3 G	IPP111N15N3 G	IPS060N03L G
IPI600N25N3 G	IPP052NE7N3 G	IPP114N03L G	IPS075N03L G
IPI80CN10N G	IPP055N03L G	IPP114N12N3 G	IPS090N03L G
IPP015N04N G	IPP057N06N3 G	IPP120N06N G	IPS105N03L G
IPP020N06N	IPP057N08N3 G	IPP126N10N3 G	IPS110N12N3 G
IPP023N04N	IPP05CN10L G	IPP12CN10L G	IPS118N10N G
IPP023N04N G	IPP05CN10N G	IPP139N08N3 G	IPS12CN10L G
IPP023NE7N3 G	IPP060N06N	IPP147N03L G	IPS135N03L G
IPP024N06N3 G	IPP062NE7N3 G	IPP147N12N3 G	IPT004N03L
IPP028N08N3 G	IPP065N03L G	IPP16CN10L G	IPT007N06N
IPP029N06N	IPP06CN10L G	IPP16CN10N G	IPT020N10N3
IPP030N10N3 G	IPP070N08N3 G	IPP180N10N3 G	IPT059N15N3
IPP032N06N3 G	IPP072N10N3 G	IPP200N15N3 G	IPU135N08N3 G
IPP034N03L G	IPP075N15N3 G	IPP200N25N3 G	IRF1010N
IPP034NE7N3 G	IPP076N12N3 G	IPP230N06L3 G	IRF1010NS
IPP037N06L3 G	IPP080N03L G	IPP260N06N3 G	IRF1310
IPP037N08N3 G	IPP084N06L3 G	IPP26CN10N G	IRF250
IPP040N06N	IPP085N06L G	IPP320N20N3 G	IRF2505S

Multisim 14.1 Base Edition Components

IRF3205	IRFE130	IRFP2410	IRFZ46NS
IRF3205S	IRFF110	IRFP244	IRFZ48N
IRF3710	IRFG110	IRFP250	IRFZ48NS
IRF3710S	IRFI1010N	IRFP260	IRG4BC10U
IRF510	IRFI3710	IRFP264	IRG4BC10UD
IRF520	IRFI520N	IRFP3710	IRG4BC15UD
IRF520N	IRFI5210	IRFP5210	IRG4BC20U
IRF520NS	IRFI5305	IRFPG40	IRG4BC40S
IRF5210	IRFI530N	IRFR110	IRG4BC40U
IRF5210S	IRFI540N	IRFR1205	IRG4BC40W
IRF5305	IRFI840G	IRFR120N	IRG4PC30U
IRF5305S	IRFI840GLC	IRFR3910	IRG4RC10K
IRF530N	IRFIZ44N	IRFR4105	IRG4RC10KD
IRF530NS	IRFIZ46N	IRFU110	IRG4RC10U
IRF540	IRFIZ48N	IRFU1205	IRG4RC10UD
IRF540N	IRFM140	IRFU120N	IRGBC20F
IRF540NS	IRFM150	IRFU2605	IRGBC20K
IRF541	IRFM9140	IRFU3910	IRGBC20S
IRF7201	IRFN054	IRFU4105	IRGBC20U
IRF7403	IRFP044N	IRFZ24N	IRGBC30F
IRF7404	IRFP048N	IRFZ24NS	IRGBC30K
IRF7413	IRFP054N	IRFZ34N	IRGBC30UD2
IRF830	IRFP064	IRFZ44N	IRGLC60KD1
IRF840	IRFP064N	IRFZ44NS	IRGPC20F
IRF9530	IRFP140N	IRFZ46N	IRGPC20U

Multisim 14.1 Base Edition Components

IRGPC40K	IRL530N	IRLR3303	J2N5905
IRGPC40UD2	IRL530NS	IRLU024N	J2N5906
IRGPC50K	IRL540	IRLU2703	J2N5907
IRGPC50M	IRLI2203G	IRLU2705	J2N5908
IRGPH40K	IRLI2203N	IRLU2905	J2N5909
IRGPH50K	IRLI2505	IRLU3103	J2N5911
IRGPH50M	IRLI2703	IRLU3303	J2N5912
IRL2203	IRLI2910	IRLZ34N	J2N6483
IRL2203NS	IRLI3103	IRLZ34NS	J2N6484
IRL2203S	IRLI3303	IRLZ44N	J2N6485
IRL2505	IRLI3803	J108	J308
IRL2505S	IRLI530N	J109	J309
IRL2703	IRLIZ24N	J110	J310
IRL2703S	IRLIZ34N	J111	J401
IRL2910	IRLL3303	J112	J402
IRL2910S	IRLP150	J113	J403
IRL3103	IRLP2203	J174	J404
IRL3103S	IRLP2505	J175	J405
IRL3303	IRLP3705	J176	J406
IRL3303S	IRLP3803	J177	J410
IRL3705	IRLR024N	J210	J411
IRL3705N	IRLR2703	J211	J412
IRL3705NS	IRLR2705	J212	JAN2N2907A
IRL3803	IRLR2905	J2N5902	JAN2N3700
IRL3803S	IRLR3103	J2N5904	JAN2N4029

Multisim 14.1 Base Edition Components

JAN2N4033	L6208_DIP24	LATCH_D2	LF155H
JANTX2N2907A	L6208_SO24	LATCH_D4_SR_OE	LF155H/883
JANTX2N3700	L6208P_SO36	LATCH_SR	LF156AH
JANTX2N4029	L6234_DIP20	LATTICE-	LF156AH/883
JANTX2N4033	L6234P_SO20	ispDOWNLOAD- HDR	LF156H
JANTXV2N2907A	L6375_DIP8	LATTICE-	LF156H/883
JANTXV2N3700	L6375_SO20	ispDOWNLOAD- USB-HDR	LF157AH/883
JANTXV2N4029	L64210GC-15	LC03-6R2G	LF157H/883
JANTXV2N4033	L64210GC-20	LD102A	LF255H
JFET_N	L64210JC-15	LD103A	LF256H
JFET_P	L64210JC-20	LD106	LF257H
JK_FF	L64210NC-15	LED	LF347BD
JK_FF_NEGSR	L64210NC-20	LED_blue	LF347BN
L6201_SO20	L64211GC-15	LED_green	LF347D
L6201P_SO20	L64211GC-20	LED_ir	LF347M
L6202_DIP18	L64211NC-15	LED_orange	LF347N
L6203_ZIP11	L64211NC-20	LED_red	LF351D
L6205_DIP20	L6911C_SO20	LED_yellow	LF351M
L6205_SO20	L6911D_SO20	LF13741H	LF351N
L6206_DIP24	L6911E_SO20	LF147D/883	LF351P
L6206_SO24	LA_CARRY_GEN	LF147J	LF353D
L6206P_SO36	LA_CARRY_GEN	LF147J/883	LF353H
L6207_DIP24	LAMP	LF155AH	LF353M
L6207_SO24	LAMP_VIRTUAL	LF155AH/883	LF353N
L6207P_SO36	LATCH_D		LF353P

Multisim 14.1 Base Edition Components

LF355AH	LF411CJG	LF441MH/883	LH0021K
LF355BM	LF411CN	LF442ACN	LH0022CD
LF355BN	LF411CP	LF442AMH	LH0022CH
LF355H	LF411ID	LF442CD	LH0024CH
LF355M	LF411IP	LF442CH	LH0024H
LF355N	LF411MH	LF442CJ	LH0024H-MIL
LF356AH	LF411MH/883	LF442CM	LH0032CG
LF356BM	LF411MWG/883	LF442CN	LH0032G
LF356BN	LF412ACH	LF442MH	LH0032G/883
LF356H	LF412ACN	LF442MH/883	LH0041CG
LF356M	LF412AMH	LF444ACN	LH0041CJ
LF356M/NOPB	LF412CD	LF444AMD	LH0041G
LF356N	LF412CH	LF444CD	LH0042CH
LF356N/NOPB	LF412CJG	LF444CJ	LH0042H
LF357AH	LF412CN	LF444CM	LH0042H-MIL
LF357BN	LF412CP	LF444CN	LH0062CD
LF357H	LF412MH	LF444MD/883	LH0062CH
LF357M	LF412MH/883	LF451CM	LH0062D
LF357N	LF412MJ/883	LF453CM	LH0062H
LF400	LF441AMH	LH0003CH	LH0101ACK
LF411ACH	LF441CD	LH0003H	LH0101AK
LF411ACN	LF441CH	LH0004CH	LH0101AK-MIL
LF411AMH	LF441CJ	LH0004H	LH0101CK
LF411CD	LF441CM	LH0004H-MIL	LH0101K
LF411CH	LF441CN	LH0021CK	LH0101K-MIL

Multisim 14.1 Base Edition Components

LH1041G	LM101AU/883	LM1084IT- ADJ/NOPB	LM108H
LH4161	LM101AW		LM108H/883
LH4162	LM101AW/883	LM1085IS-12/NOPB	LM108J
LHV870LC/NOPB	LM101D	LM1085IS- 3.3/NOPB	LM108J/883
LIMIT_NC	LM101F	LM1085IS- 5.0/NOPB	LM108J8
LIMIT_NO	LM101F/883		LM108J-8
LINKSYS-WRT54G- HD	LM101H	LM1085IS- ADJ/NOPB	LM108J8/883
LM101AD	LM101H/883	LM1085IT-12/NOPB	LM108J-8/883
LM101AD/883	LM101J-14	LM1085IT- 3.3/NOPB	LM108JG
LM101AF	LM101J-14/883		LM108JG/883
LM101AF/883	LM107J	LM1085IT- 5.0/NOPB	LM108L
LM101AFK	LM107JG		LM108P
LM101AFK/883	LM107JG/883	LM1085IT- ADJ/NOPB	LM10BH
LM101AH	LM107U	LM108AD	LM10BLH
LM101AH/883	LM107W	LM108AH	LM10CH
LM101AJ	LM107W/883	LM108AH/883	LM10CLH
LM101AJ/883	LM1084IS- 3.3/NOPB	LM108AJ	LM10CLN
LM101AJ-14	LM1084IS- 5.0/NOPB	LM108AJ/883	LM10CLN8
LM101AJ-14/883	LM1084IS- ADJ/NOPB	LM108AJ-8	LM10CLWM
LM101AJ8		LM108AJ-8/883	LM10CN
LM101AJG	LM1084IT- 3.3/NOPB	LM108AJG	LM10CN8
LM101AJG/883		LM108AL	LM10CWM
LM101AP	LM1084IT- 5.0/NOPB	LM108AP	LM10H
LM101AU		LM108D	LM10H/883
		LM108D/883	

Multisim 14.1 Base Edition Components

LM1117DT- 1.8/NOPB	LM1117MP- 2.5/NOPB	LM118H	LM124E
LM1117DT- 2.5/NOPB	LM1117MPX- ADJ/NOPB	LM118H/883	LM124E/883
LM1117DT- 3.3/NOPB	LM1117SX- 3.3/NOPB	LM118J	LM124FK
LM1117DT- 5.0/NOPB	LM1117SX- 5.0/NOPB	LM118J/883	LM124J
LM1117DTX- ADJ/NOPB	LM1117SX- ADJ/NOPB	LM118J8	LM124J/883
LM1117IDTX- ADJ/NOPB	LM1117T-2.5/NOPB	LM118J-8	LM124N
LM1117ILD- ADJ/NOPB	LM1117T-3.3/NOPB	LM118J8/883	LM124W
LM1117IMP- 3.3/NOPB	LM1117T-5.0/NOPB	LM118J-8/883	LM124W/883
LM1117IMP- 5.0/NOPB	LM1117T- ADJ/NOPB	LM118JG	LM12CLK
LM1117IMPX- ADJ/NOPB	LM111E	LM118L	LM12LK
LM1117LD- 1.8/NOPB	LM111E/883	LM118P	LM13700AN
LM1117LD- 2.5/NOPB	LM111H	LM11CH	LM13700M
LM1117LD- 3.3/NOPB	LM111J-14	LM11CLH	LM13700N
LM1117LDX- ADJ/NOPB	LM111J-8	LM11CLN	LM139AJ
LM1117MP- 1.8/NOPB	LM111W	LM11H	LM139AW
	LM112H	LM124AD	LM139E
	LM112H/883	LM124AE	LM139J
	LM117HVH	LM124AE/883	LM139W
	LM117HVKSTL/883	LM124AFK	LM144H
	LM118D	LM124AJ	LM144H/883
	LM118FK	LM124AJ/883	LM146J
		LM124AN	LM146J/883
		LM124AW/883	LM149J
		LM124AWG/883	LM149J/883
		LM124D	LM158AD

Multisim 14.1 Base Edition Components

LM158AFK	LM207P	LM216F	LM22670QTJ- ADJ/NOPB
LM158AH	LM208AD	LM216H	
LM158AH/883	LM208AH	LM218D	LM22670TJ- 5.0/NOPB
LM158AJ	LM208AJ	LM218H	LM22670TJ- ADJ/NOPB
LM158AJG	LM208AJ-8	LM218JG	
LM158AN	LM208AN	LM218P	LM22671MR- 5.0/NOPB
LM158AP	LM208AP	LM221H	LM22671MR- ADJ/NOPB
LM158AWG/883	LM208D	LM224AD	
LM158D	LM208H	LM224AJ	LM22671QMR- ADJ/NOPB
LM158FK	LM208J	LM224AN	
LM158H	LM208J-8	LM224AP	LM22672MR- ADJ/NOPB
LM158J	LM208N	LM224D	LM22672QMR- ADJ/NOPB
LM158JG	LM208P	LM224DG	
LM158N	LM211H	LM224DR2G	LM22673MR- 5.0/NOPB
LM158P	LM211J-8	LM224DTBG	LM22673MR- ADJ/NOPB
LM160H	LM211M	LM224DTBR2G	
LM160J	LM21212MH- 1/NOPB	LM224J	LM22673TJ- 5.0/NOPB
LM160J-14		LM224N	
LM1877M-9	LM21212MH- 2/NOPB	LM224NG	LM22673TJ- ADJ/NOPB
LM1877N-9	LM21215MH/NOPB	LM224P	LM22674MR- 5.0/NOPB
LM20123MH/NOPB	LM212H	LM22670MR- 5.0/NOPB	LM22674MR- ADJ/NOPB
LM202H	LM216AD	LM22670MR- ADJ/NOPB	
LM207D	LM216AF		LM22674QMR- ADJ/NOPB
LM207H	LM216AH	LM22670QMR- ADJ/NOPB	
LM207J	LM216D		

Multisim 14.1 Base Edition Components

LM22675MR- 5.0/NOPB	LM22679TJ- 5.0/NOPB	LM258AJG	LM2596T-12/LF03
LM22675MR- ADJ/NOPB	LM22679TJ- ADJ/NOPB	LM258AN	LM2596T-12/NOPB
LM22675QMR- ADJ/NOPB	LM22680MR- ADJ/NOPB	LM258AP	LM2596T-3.3/LF03
LM22676MR- 5.0/NOPB	LM22680QMR- ADJ/NOPB	LM258D	LM2596T-3.3/NOPB
LM22676MR- ADJ/NOPB	LM239AJ	LM258DG	LM2596T-5.0/LF03
LM22676QMR- ADJ/NOPB	LM239DG	LM258DMR2G	LM2596T-5.0/NOPB
LM22676QMR- ADJ/NOPB	LM239DR2G	LM258DR2G	LM26420XMH/NOP B
LM22676QTJ- ADJ/NOPB	LM239DTBR2G	LM258H	LM26420XSQ/NOP B
LM22676TJ- 5.0/NOPB	LM239J	LM258JG	LM26420YMH/NOP B
LM22676TJ- ADJ/NOPB	LM239NG	LM258N	LM26420YM/NOP B
LM22677QTJ- ADJ/NOPB	LM246J	LM258NG	LM26420YSQ/NOP B
LM22677TJ- 5.0/NOPB	LM25018MR/NOPB	LM258P	LM2673S- ADJ/NOPB
LM22677TJ- ADJ/NOPB	LM25018SD/NOPB	LM2592HVS- ADJ/NOPB	LM2673SD- ADJ/NOPB
LM22677TJ- 5.0/NOPB	LM25115MT/NOPB	LM2592HVT- ADJ/NOPB	LM2673T- ADJ/NOPB
LM22677TJ- ADJ/NOPB	LM25115SD/NOPB	LM2594HVM- ADJ/NOPB	LM2675LD- ADJ/NOPB
LM22678QTJ- ADJ/NOPB	LM25116MH/NOPB	LM2594HVN- ADJ/NOPB	LM2675M- ADJ/NOPB
LM22678TJ- 5.0/NOPB	LM25119PSQ/NOP B	LM2594M- ADJ/NOPB	LM2675N- ADJ/NOPB
LM22678TJ- ADJ/NOPB	LM25574MT/NOPB	LM2594N- ADJ/NOPB	LM2678S-3.3/NOPB
	LM25575MH/NOPB	LM2596S-3.3/NOPB	
	LM25576MH/NOPB	LM2596S-5.0/NOPB	
	LM258AD	LM2596SX- 12/NOPB	
	LM258AH		

Multisim 14.1 Base Edition Components

LM2678T-3.3/NOPB	LM2830ZMF/NOPB	LM2842YQMK/NOPB	LM2902MT
LM2679S-ADJ/NOPB	LM2830ZSD/NOPB		LM2902N
LM2679SD-ADJ/NOPB	LM2831XMF/NOPB	LM2852XMXA-0.8/NOPB	LM2902NG
LM2679T-ADJ/NOPB	LM2831XSD/NOPB	LM2852YMXA-0.8/NOPB	LM2902VD
	LM2831YMF/NOPB		LM2902VDG
	LM2831YSD/NOPB	LM2853MH-3.0/NOPB	LM2902VDR2G
LM27313XMF/NOPB	LM2831ZMF/NOPB		LM2902VDTBG
	LM2831ZSD/NOPB	LM2854MH-1000/NOPB	LM2902VDTBR2G
LM2731XMF/NOPB	LM2832XMY/NOPB	LM2854MH-500/NOPB	LM2902VN
LM2731YMF/NOPB	LM2832XSD/NOPB		LM2903DG
LM27341MY/NOPB	LM2832YMY/NOPB	LM2878P	LM2903DMR2G
LM27341SD/NOPB	LM2832YSD/NOPB	LM2900N	LM2903DR2
LM2734XMK/NOPB	LM2832ZMY/NOPB	LM2901DG	LM2903DR2G
LM2734YMK/NOPB	LM2832ZSD/NOPB	LM2901DR2G	LM2903NG
LM2735XMF/NOPB	LM2841XMK-ADJL/NOPB	LM2901DTBR2G	LM2904ADMR2G
LM2735XMY/NOPB		LM2901NG	LM2904AN
LM2735XSD/NOPB	LM2841XQMK/NOPB	LM2901VDG	LM2904ANG
LM2735YMF/NOPB		LM2901VDR2G	LM2904D
LM2735YMY/NOPB	LM2841YMK-ADJL/NOPB	LM2901VDTBR2G	LM2904DG
LM2735YSD/NOPB	LM2841YQMK/NOPB	LM2901VNG	LM2904DMR2G
LM27402MH/NOPB		LM2902DG	LM2904DR2G
LM27402SQ/NOPB	LM2842XMK-ADJL/NOPB	LM2902DR2G	LM2904ITP
LM27403SQ/NOPB		LM2902DTBG	LM2904M
LM2743MTC/NOPB	LM2842XQMK/NOPB	LM2902DTBR2G	LM2904N
LM2830XMF/NOPB	LM2842YMK-ADJL/NOPB	LM2902M	LM2904NG

Multisim 14.1 Base Edition Components

LM2904P	LM2940IMPX-8.0/NOPB	LM307N	LM318J8
LM2904PW		LM307P	LM318J-8
LM2904QD	LM2940LD-12/NOPB	LM308AD	LM318M
LM2904QP	LM2940LD-5.0/NOPB	LM308AH	LM318N
LM2904VD		LM308AJ	LM318N8
LM2904VDG	LM2940S-10/NOPB	LM308AJ-8	LM318P
LM2904VDMR2G	LM2940S-12/NOPB	LM308AN	LM318S8
LM2904VDR2G	LM2940S-5.0/NOPB	LM308AN8	LM321AH
LM2904VN	LM2940S-8.0/NOPB	LM308D	LM321H
LM2904VNG	LM2940S-9.0/NOPB	LM308H	LM324AD
LM2924M	LM2940T-10.0/NOPB	LM308J	LM324ADG
LM2924N	LM2940T-	LM308J-8	LM324ADR2G
LM293D	12.0/NOPB	LM308M	LM324ADTBG
LM293DG	LM2940T-5.0/NOPB	LM308N	LM324ADTBR2G
LM293DMR2G	LM2940T-8.0/NOPB	LM308N8	LM324AJ
LM293DR2G	LM2940T-9.0/NOPB	LM3100MH/NOPB	LM324AM
LM2940IMP-10/NOPB	LM2941LD/NOPB	LM3102MH/NOPB	LM324AN
	LM2941S/NOPB	LM3102TL-1/NOPB	LM324ANG
LM2940IMP-12/NOPB	LM2941T/LF03	LM311H	LM324AP
LM2940IMP-15/NOPB	LM2941T/NOPB	LM311M	LM324APWLE
	LM301AD	LM311N	LM324D
LM2940IMP-5.0/NOPB	LM301AJ8	LM311N-14	LM324DBLE
	LM301AP	LM312H	LM324DG
LM2940IMP-9.0/NOPB	LM3046M	LM318D	LM324DR2G
	LM307D	LM318H	LM324DTBG

Multisim 14.1 Base Edition Components

LM324DTBR2G	LM3481MM/NOPB	LM358AN	LM393DR2G
LM324J	LM3485MM/NOPB	LM358AP	LM393NG
LM324M	LM3489MM/NOPB	LM358BP	LM4030AMF- 2.5/NOPB
LM324MT	LM348D	LM358D	LM4030AMF- 4.096/NOPB
LM324N	LM348N	LM358DB	LM4030BMF- 2.5/NOPB
LM324NG	LM348PW	LM358DG	LM4030BMF- 4.096/NOPB
LM324P	LM34910CSD/NOPB	LM358DMR2G	LM4030CMF- 2.5/NOPB
LM324PWLE	LM34910SD/NOPB	LM358DR2G	LM4030CMF- 4.096/NOPB
LM324x2DBLE	LM34914SD/NOPB	LM358H	LM4030CMF- 2.5/NOPB
LM3301N	LM34917ATL/NOPB	LM358J	LM4030CMF- 4.096/NOPB
LM3302N	LM34919CQSD/NO PB	LM358JG	LM4040AIM3- 10.0/NOPB
LM339AJ	LM34919CQTL/NOP B	LM358M	LM4040AIM3- 2.0/NOPB
LM339AM	LM34919TL/NOPB	LM358N	LM4040AIM3- 2.5/NOPB
LM339AN	LM34925MR/NOPB	LM358NG	LM4040AIM3- 3.0/NOPB
LM339DG	LM34925SD/NOPB	LM358P	LM4040AIM3- 4.1/NOPB
LM339DR2G	LM34926MR/NOPB	LM358PW	LM4040AIM3- 5.0/NOPB
LM339DTBR2G	LM34926SD/NOPB	LM358TP	LM4040AIZ- 10.0/NOPB
LM339J	LM34927MR/NOPB	LM359J	LM4040AIZ- 2.5/NOPB
LM339M	LM34927SD/NOPB	LM359M	
LM339N	LM358AD	LM359N	
LM339NG	LM358ADR2G	LM3900D	
LM344H	LM358AH	LM3900M	
LM346J	LM358AJG	LM3900N	
LM346M	LM358AM	LM393DG	
LM346N		LM393DMR2G	

Multisim 14.1 Base Edition Components

LM4040AIZ- 4.1/NOPB	LM4040BIZ- 5.0/NOPB	LM4040DEM3- 2.5/NOPB	LM4040EIM7- 2.0/NOPB
LM4040AIZ- 5.0/NOPB	LM4040CEM3- 2.5/NOPB	LM4040DEM3- 3.0/NOPB	LM4041AIM3- 1.2/NOPB
LM4040BIM3- 10.0/NOPB	LM4040CEM3- 3.0/NOPB	LM4040DEM3- 5.0/NOPB	LM4041AIZ- 1.2/NOPB
LM4040BIM3- 2.0/NOPB	LM4040CEM3- 5.0/NOPB	LM4040DIM3- 10.0/NOPB	LM4041BIM3- 1.2/NOPB
LM4040BIM3- 2.5/NOPB	LM4040CIM3- 10.0/NOPB	LM4040DIM3- 4.1/NOPB	LM4041BIM7- 1.2/NOPB
LM4040BIM3- 3.0/NOPB	LM4040CIM3- 2.0/NOPB	LM4040DIM3- 8.2/NOPB	LM4041BIZ- 1.2/NOPB
LM4040BIM3- 4.1/NOPB	LM4040CIM3- 4.1/NOPB	LM4040DIM7- 2.0/NOPB	LM4041CEM3- 1.2/NOPB
LM4040BIM3- 5.0/NOPB	LM4040CIM3- 8.2/NOPB	LM4040DIM7- 2.5/NOPB	LM4041CEM3- ADJ/NOPB
LM4040BIM3- 8.2/NOPB	LM4040CIM7- 2.0/NOPB	LM4040DIM7- 5.0/NOPB	LM4041CIM7- 1.2/NOPB
LM4040BIM7- 2.0/NOPB	LM4040CIM7- 2.5/NOPB	LM4040DIZ- 10.0/NOPB	LM4041CIM7- ADJ/NOPB
LM4040BIM7- 2.5/NOPB	LM4040CIZ- 10.0/NOPB	LM4040DIZ- 2.5/NOPB	LM4041CIZ- 1.2/NOPB
LM4040BIM7- 5.0/NOPB	LM4040CIZ- 2.5/LFT8	LM4040DIZ- 4.1/NOPB	LM4041CIZ- ADJ/NOPB
LM4040BIZ- 10.0/NOPB	LM4040CIZ- 4.1/NOPB	LM4040DIZ- 5.0/LFT1	LM4041DEM3- 1.2/NOPB
LM4040BIZ- 2.5/NOPB	LM4040CIZ- 5.0/NOPB	LM4040EEM3- 2.5/NOPB	LM4041DEM3- ADJ/NOPB
LM4040BIZ- 4.1/NOPB	LM4040DEM3- 2.0/NOPB	LM4040EEM3- 3.0/NOPB	LM4041DIM7- 1.2/NOPB

Multisim 14.1 Base Edition Components

LM4041DIM7- ADJ/NOPB	LM4050BEM3- 5.0/NOPB	LM4562MA	LM5122MH/NOPB
		LM4562NA	LM5160DNTJ
LM4041DIZ- 1.2/NOPB	LM4050BEM3- 8.2/NOPB	LM46000PWP	LM536023QPWPTQ 1
LM4041DIZ- ADJ/LFT1	LM4050BIM3X- 2.0/NOPB	LM46001PWP	LM536025QPWPTQ 1
LM4041DIZ- ADJ/NOPB	LM4050CEM3- 2.5/NOPB	LM5001MA/NOPB	LM53602AQPWPTQ 1
		LM5001SD/NOPB	
LM4041EEM3- 1.2/NOPB	LM4050CEM3- 5.0/NOPB	LM5002MA/NOPB	LM536033QPWPTQ 1
LM4041EIM7- 1.2/NOPB	LM4050CIM3- 10/NOPB	LM5002SD/NOPB	LM536035QPWPTQ 1
		LM5008MM/NOPB	
LM4050AEM3- 10/NOPB	LM4050CIM3- 4.1/NOPB	LM5008SDC/NOPB	LM53603AQPWPTQ 1
		LM5009MM/NOPB	LM555CM
LM4050AEM3- 2.0/NOPB	LM4050CIM3X- 2.0/NOPB	LM5009SDC/NOPB	LM555CN
LM4050AEM3- 2.5/NOPB	LM4051AIM3- 1.2/NOPB	LM5010AMH/NOPB	LM556CM
		LM5010ASD/NOPB	LM556CN
LM4050AEM3- 5.0/NOPB	LM4051AIM3- ADJ/NOPB	LM5085MM/NOPB	LM5574MT/NOPB
LM4050AEM3- 8.2/NOPB	LM4250CH	LM5085MY/NOPB	LM5575MH/NOPB
	LM4250CM	LM5085SD/NOPB	LM5576MH/NOPB
LM4050AIM3- 4.1/NOPB	LM4250CN	LM5088MH- 2/NOPB	LM607ACH
LM4050BEM3- 10/NOPB	LM4250J-MIL	LM5116MH/NOPB	LM607ACN
	LM43600PWP	LM5117PMH/NOPB	LM607AMH
LM4050BEM3- 2.5/NOPB	LM43601PWP	LM5117PSQ/NOPB	LM607BCH
	LM43602PWP	LM5119PSQ/NOPB	LM607BCN
LM4050BEM3- 4.1/NOPB	LM43603PWP	LM5121MH/NOPB	LM607BMH
	LM4562HA		

Multisim 14.1 Base Edition Components

LM607CH	LM6164E/883	LM6261J	LM637ACH
LM607CN	LM6164J	LM6261M	LM637AMH
LM6118E/883	LM6164J/883	LM6261N	LM637BCH
LM6118J/883	LM6164W/883	LM6262M	LM637BMH
LM6118N	LM6164WG/883	LM6262N	LM637CH
LM6132AIM	LM6165E/883	LM6264J	LM637CN
LM6132BIM	LM6165J	LM6264N	LM709AH
LM6132BIN	LM6165J/883	LM6265J	LM709CH
LM6142AIM	LM6165W/883	LM6265N	LM709CN
LM6142AIN	LM6165WG/883	LM627ACH	LM709CN-8
LM6142AMJ-MLS	LM6171AIM	LM627AMH	LM709H
LM6142BIM	LM6171BIM	LM627BCH	LM710AMJ
LM6142BIN	LM6171BIN	LM627BMH	LM710AMW
LM6152ACM	LM6172AMJFQML	LM627CH	LM710CH
LM6152BCM	LM6172AMWGFQ ML	LM627CN	LM710CN
LM6161E/883	LM6172IM	LM6313N	LM710H
LM6161J	LM6172IN	LM6361J	LM7121IM
LM6161J/883	LM6181IM	LM6361M	LM7121IM5
LM6161W/883	LM6181IN	LM6361N	LM7131ACM
LM6161WG/883	LM6211MF	LM6362M	LM7131ACM5
LM6162E/883	LM6218AN	LM6362N	LM715CH
LM6162J/883	LM6218AWM	LM6364M	LM715CJ
LM6162N	LM6218N	LM6364N	LM715MH
LM6162W/883	LM6218WM	LM6365M	LM715MJ
LM6162WG/883		LM6365N	LM7171AIM

Multisim 14.1 Base Edition Components

LM7171AIN	LM741CM	LM7824CT	LMC6001BIN
LM7171AMJFQML	LM741CN	LM7905CT	LMC6022IM
LM7171BIM	LM741EH	LM7909CT	LMC6024IM
LM7171BIN	LM741EN	LM7912CT	LMC6032IM
LM725AH	LM741H	LM7915CT	LMC6032IN
LM725AH/883	LM741H/883	LM7918CT	LMC6034IM
LM725CH	LM741J	LM7924CT	LMC6035IBP
LM725CN	LM741J/883	LM809M3- 2.63/NOPB	LMC6035IM
LM725H	LM741J-14/883		LMC6035IMM
LM725H/883	LM741W/883	LM809M3- 2.93/NOPB	LMC6035ITL
LM7301IM	LM747AH	LM809M3- 3.08/NOPB	LMC6036IM
LM7301IM5	LM747AJ		LMC6036IMT
LM7321MA	LM748CH	LM809M3- 4.38/NOPB	LMC6041AIM
LM7321MF	LM748CJ	LM809M3- 4.63/NOPB	LMC6041AIN
LM7322MA	LM748CN		LMC6041IM
LM7322MM	LM748H	LM8261M5	LMC6041IN
LM7332MA	LM759CH	LM8272MM	LMC6042AIM
LM7332MM	LM759CP	LM833D	LMC6042AIN
LM7341MF	LM759H/883	LM833DG	LMC6042IM
LM7372IMA	LM759MH	LM833DR2G	LMC6042IN
LM7372MR	LM7805CT	LM833NG	LMC6044AIM
LM741AH/883	LM7809CT	LMC555CH	LMC6044AIN
LM741AJ-14/883	LM7812CT	LMC555CM	LMC6044IM
LM741CH	LM7815CT	LMC555CN	LMC6044IN
LM741CJ	LM7818CT	LMC6001AIN	LMC6061AIM

Multisim 14.1 Base Edition Components

LMC6061AIN	LMC6084IM	LMC6484IN	LMC6772AIMM
LMC6061AMJ/883	LMC6442AIM	LMC6484MN	LMC6772BIM
LMC6061AMN	LMC6442IM	LMC6492AEM	LMC6772BIN
LMC6061IM	LMC6442IN	LMC6492BEM	LMC7101AIM5
LMC6061IN	LMC6462AIM	LMC6494AEM	LMC7101BIM5
LMC6062AIM	LMC6462AIN	LMC6494BEM	LMC7111BIM5
LMC6062AIN	LMC6462BIM	LMC6572AIM	LMC7211AIM
LMC6062AMJ/883	LMC6462BIN	LMC6572BIM	LMC7211AIM5
LMC6062AMN	LMC6464AIM	LMC6574AIM	LMC7211BIM
LMC6062IM	LMC6464AMWG- QML	LMC6574BIM	LMC7211BIM5
LMC6062IN	LMC6464BIM	LMC660AIM	LMC7215IM
LMC6064AIM	LMC6464BIN	LMC660AIN	LMC7215IM5
LMC6064IM	LMC6482AIM	LMC660AMD	LMC7221AIM
LMC6064IN	LMC6482AIN	LMC660AMJ/883	LMC7221AIM5
LMC6081AIM	LMC6482AMJ/883	LMC660CM	LMC7221BIM
LMC6081AIN	LMC6482IM	LMC660CN	LMC7221BIM5
LMC6081AMN	LMC6482IMM	LMC662AIM	LMC7225IM5
LMC6081IM	LMC6482IN	LMC662AIN	LMC8101BP
LMC6081IN	LMC6482MN	LMC662AMD	LMC8101MM
LMC6082AIM	LMC6484AIM	LMC662AMJ/883	LMC8101TP
LMC6082AIN	LMC6484AIN	LMC662CM	LME49710HA
LMC6082AMN	LMC6484AMJ/883	LMC662CN	LME49710MA
LMC6082IM	LMC6484AMWG/8 83	LMC6762AIM	LME49710NA
LMC6082IN		LMC6762BIM	LME49720HA
LMC6084AIM	LMC6484IM	LMC6772AIM	LME49720MA

Multisim 14.1 Base Edition Components

LME49720NA	LMH6555SQ	LMH6643MA	LMH6702J-QML
LME49740MA	LMH6559MA	LMH6643MAXEP	LMH6702MA
LME49740NA	LMH6559MF	LMH6643MM	LMH6702MF
LME49990MA/NOPB	LMH6601MG	LMH6644MA	LMH6703MA
B	LMH6609MA	LMH6644MAXEP	LMH6703MF
LMH3401IRMSR	LMH6609MF	LMH6644MT	LMH6704MA/NOPB
LMH5401IRMSR	LMH6611MK	LMH6645MA	LMH6704MF/NOPB
LMH6321MR	LMH6612MA	LMH6645MA/NOPB	LMH6714J-QML
LMH6321TS	LMH6618MK	LMH6645MF	LMH6714MA
LMH6502MA	LMH6619MA	LMH6645MF/NOPB	LMH6714MF
LMH6502MT	LMH6622MA	LMH6646MA	LMH6715JFQML
LMH6503MA	LMH6622MM	LMH6646MM	LMH6715MA
LMH6503MT	LMH6624J-QML	LMH6647MA	LMH6718MA
LMH6505MA	LMH6624MA	LMH6647MF	LMH6720J-QML
LMH6505MM	LMH6624MF	LMH6654MA/NOPB	LMH6720MA
LMH6521SQ/NOPB	LMH6628JFQML	LMH6654MF/NOPB	LMH6720MF
LMH6550MA	LMH6628MA	LMH6655MA	LMH6722J-QML
LMH6550MM	LMH6628WGFQML	LMH6655MM	LMH6722MA
LMH6551MA	LMH6629MF	LMH6657MF	LMH6722MT
LMH6551MM	LMH6629SD	LMH6657MG	LMH6723MA
LMH6552MA	LMH6639MA	LMH6658MA/NOPB	LMH6723MF
LMH6552SD	LMH6639MF	LMH6658MM/NOPB	LMH6733MQ
LMH6553MR	LMH6642MA	B	LMH6738MQ
LMH6553SD	LMH6642MF	LMH6672MA	LMH6739MQ
LMH6554LE	LMH6642MFXEP	LMH6672MR	LMP2011MA

Multisim 14.1 Base Edition Components

LMP2011MF	LMP7702MA	LMP8601MA	LMR10515YSD/NOP B
LMP2015MA	LMP7702MM	LMP8601QMA	LMR10520XSD/NOP B
LMP2015MF	LMP7704MA	LMP8602MA	LMR10520YSD/NOP B
LMP2016MA	LMP7704MT	LMP8602MM	LMR12010XMK/NO PB
LMP2016MM	LMP7707MF	LMP8602QMA	LMR12010YMK/NO PB
LMP2021MA	LMP7708MM	LMP8602QMM	LMR14006XDDCR
LMP2021MF	LMP7709MT	LMP8603MA	LMR14006YDDCR
LMP2022MA	LMP7711MK	LMP8603MM	LMR14020SDDA
LMP2022MM	LMP7712MM	LMP8603QMA	LMR14203XMK/NO PB
LMP2231AMA	LMP7715MF	LMP8603QMM	LMR14206XMK/NO PB
LMP2231AMF	LMP7716MM	LMP8645HVMK	LMR16006XDDCR
LMP2231BMA	LMP7717MA	LMP8645MK	LMR16006YDDCR
LMP2231BMF	LMP7717MF	LMP8671MA/NOPB	LMR24210TL/NOPB
LMP2232AMA	LMP7718MA	LMP8672MA/NOPB	LMR24220TL/NOPB
LMP2232AMM	LMP7718MM	LMP8674MA/NOPB	LMR61428XMM/N OPB
LMP2232BMA	LMP7731MA	LMR10510XMF/NO PB	LMR62014XMF/NO PB
LMP2232BMM	LMP7731MF	LMR10510YMF/NO PB	LMR62421XMF/NO PB
LMP2234AMA	LMP7732MA	LMR10510YSD/NOP B	LMR62421XSD/NOP B
LMP2234AMT	LMP7732MM	LMR10515XMF/NO PB	
LMP2234BMA	LMP8270MA	LMR10515XSD/NOP B	
LMP2234BMT	LMP8271MA	LMR10515YMF/NO PB	
LMP7300MA	LMP8272MA		
LMP7300MM	LMP8275MA		
LMP7701MA	LMP8276MA		
LMP7701MF	LMP8277MA		

Multisim 14.1 Base Edition Components

LMR64010XMF/NOPB	LMV2011MF	LMV601MG/NOPB	LMV7275MG/NOPB
PB	LMV321M5	LMV602MA/NOPB	LMV7291MG
LMR70503TM/NOPB	LMV321M5/NOPB	LMV602MM/NOPB	LMV751M5
LMS1585ACS-1.5/NOPB	LMV321M7	LMV604MA/NOPB	LMV761MA
	LMV321M7/NOPB	LMV604MT/NOPB	LMV761MF
LMS1585ACS-3.3/NOPB	LMV324M	LMV611MF/NOPB	LMV771MG
	LMV324MT	LMV611MG/NOPB	LMV772MA
LMS1585ACSX-ADJ/NOPB	LMV331M5	LMV612MA/NOPB	LMV772MM
	LMV331M7	LMV612MM/NOPB	LMV772QMM
LMS1585ACT-1.5/NOPB	LMV339M	LMV614MA/NOPB	LMV774MT
	LMV339MT	LMV614MT/NOPB	LMV791MK
LMS1585AIS-1.5/NOPB	LMV342MA	LMV641MA	LMV792MM
	LMV342MM	LMV641MG	LMV793MA
LMS1585AIS-3.3/NOPB	LMV358M	LMV651MG	LMV793MF
	LMV358MM	LMV652MM	LMV794MA
LMS1587CS-1.5/NOPB	LMV393M	LMV654MT	LMV794MM
	LMV393MM	LMV711M6	LMV796MF
LMS1587CS-3.3/NOPB	LMV431AIM5/NOPB	LMV716MM	LMV797MM
	B	LMV7219M5	LMV821M5
LMS1587CS-ADJ/NOPB	LMV431AIMF/NOPB	LMV7219M7	LMV821M7
	B	LMV721M5	LMV822M
LMS1587CT-3.3/NOPB	LMV431AIZ/LFT3	LMV721M7	LMV822MM
	LMV431AIZ/NOPB	LMV7271MF	LMV824M
LMS1587IT-1.5/NOPB	LMV551MG	LMV7271MG	LMV824MT
	LMV552MM	LMV7275MF/NOPB	LMV831MG
LMV2011MA	LMV554MT		

Multisim 14.1 Base Edition Components

LMV832MM	LMX321AXK+	LMZ12003TZ- ADJ/NOPB	LMZ22005TZ/NOPB
LMV834MT	LMX324ASD+		LMZ22008TZ/NOPB
LMV841MG	LMX324AUD+	LMZ12008TZ/NOPB	LMZ22010TZ/NOPB
LMV842MA	LMX358AKA+	LMZ12010TZ/NOPB	LMZ23603TZ/NOPB
LMV842MM	LMX358ASA+	LMZ13608TZ/NOPB	LMZ23608TZ/NOPB
LMV844MA	LMX358AUA+	LMZ13610TZ/NOPB	LMZ23610TZ/NOPB
LMV844MT	LMZ10500SILR	LMZ14201EXTTZ/N OPB	LMZ30602RKGR
LMV851MG	LMZ10501SILR	LMZ14201HTZ/NOP B	LMZ30604RKGR
LMV852MM	LMZ10503EXTTZ/N OPB		LMZ30606RKGR
LMV854MT		LMZ14201TZ- ADJ/NOPB	LMZ31503RUQT
LMV861MG	LMZ10503TZ- ADJ/NOPB		LMZ31506HRUQR
LMV862MM	LMZ10504TZ- ADJ/NOPB	LMZ14202EXTTZ/N OPB	LMZ31506RUQR
LMV881LE/NOPB		LMZ14202HTZ/NOP B	LMZ31520RLGT
LMV931MF	LMZ10505EXTTZ/N OPB		LMZ31530RLGT
LMV931MG		LMZ14202TZ- ADJ/NOPB	LMZ31704RVQR
LMV932MA	LMZ10505TZ- ADJ/NOPB		LMZ31707RVQR
LMV932MM	LMZ12001EXTTZ/N OPB	LMZ14203EXTTZ/N OPB	LMZ31710RVQR
LMV934MA		LMZ14203HTZ/NOP B	LMZ34002RKGR
LMV934MT	LMZ12001TZ- ADJ/NOPB		LMZ35003RKGR
LMV951MK	LMZ12002EXTTZ/N OPB	LMZ14203TZ- ADJ/NOPB	LOSSLESS_LINE_TYP E1
LMV981BL		LMZ20501SILR	
LMV981MF	LMZ12002TZ- ADJ/NOPB	LMZ20502SILR	LOSSLESS_LINE_TYP E2
LMV981MG		LMZ21700SILR	LOSSY_TRANSMISSI ON_LINE
LMV981TL	LMZ12003EXTTZ/N OPB	LMZ21701SILR	
LMX321AUK+		LMZ22003TZ/NOPB	LP124J

Multisim 14.1 Base Edition Components

LP239D	LP2985ITP- 3.3/NOPB	LP2992AIM5- 1.8/NOPB	LP324M
LP239J			LP324N
LP239N	LP2985ITP- 5.0/NOPB	LP2992AIM5- 2.5/NOPB	LP339D
LP2901D	LP2989AILD- 3.3/NOPB	LP2992AIM5- 3.3/NOPB	LP339J
LP2901J			LP339M
LP2901N	LP2989AILD- 5.0/NOPB	LP2992AIM5- 5.0/NOPB	LP339N
LP2902M	LP2989AIM- 2.5/NOPB	LP2992ILD- 1.8/NOPB	LP38502ASD- ADJ/NOPB
LP2902N			LP38502ATJ- ADJ/NOPB
LP2954AIM/NOPB	LP2989AIM- 3.3/NOPB	LP2992ILD- 2.5/NOPB	LP38502SD- ADJ/NOPB
LP2985AIM5- 2.5/NOPB	LP2989AIM- 5.0/NOPB	LP2992ILD- 3.3/NOPB	LP38502TJ- ADJ/NOPB
LP2985AIM5- 3.3/NOPB	LP2989AIMM- 2.5/NOPB	LP2992ILD- 5.0/NOPB	LP38502TS- ADJ/NOPB
LP2985AIM5- 5.0/NOPB	LP2989AIMM- 3.3/NOPB	LP2992ILD- 1.5/NOPB	LP38690SD- 1.8/NOPB
LP2985AITL- 3.3/NOPB	LP2989AIMM- 5.0/NOPB	LP2992IM5- 1.5/NOPB	LP38690SD- 2.5/NOPB
LP2985AITP- 3.3/NOPB	LP2992AILD- 1.5/NOPB	LP2992IM5- 1.8/NOPB	LP38690SD- 3.3/NOPB
LP2985AITP- 5.0/NOPB	LP2992AILD- 1.8/NOPB	LP2992IM5- 2.5/NOPB	LP38690SD- 5.0/NOPB
LP2985IM5- 2.5/NOPB	LP2992AILD- 3.3/NOPB	LP2992IM5- 3.3/NOPB	LP38690SD- ADJ/NOPB
LP2985IM5- 3.3/NOPB	LP2992AILD- 5.0/NOPB	LP2992IM5- 5.0/NOPB	LP38691SD- 3.3/NOPB
LP2985IM5- 5.0/NOPB	LP2992AIM5- 1.5/NOPB	LP311M	LP38691SD- ADJ/NOPB
LP2985ITP- 2.5/NOPB		LP311N	

Multisim 14.1 Base Edition Components

LP38692MP- ADJ/NOPB	LP5907SNX- 2.85/NOPB	LPR200JC12	LT1001ACH
		LPR200JC15	LT1001ACJ8
LP38692SD- ADJ/NOPB	LP5907SNX- 3.2/NOPB	LPR200JC20	LT1001ACN8
LP38693MP- ADJ/NOPB	LP5907SNX- 4.0/NOPB	LPR200PC10	LT1001AMH/883
		LPR200PC12	LT1001AMJ8/883
LP38693SD- ADJ/NOPB	LP5907UVE- 2.85/NOPB	LPR200PC15	LT1001CH
		LPR200PC20	LT1001CJ8
LP38798SD- ADJ/NOPB	LP5907UVE- 3.2/NOPB	LPR201JC10	LT1001CN8
LP5900SD- 1.5/NOPB	LPC660AIM	LPR201JC12	LT1001CS8
	LPC660AIN	LPR201JC15	LT1001MH
LP5900SD- 2.8/NOPB	LPC660AMD	LPR201JC20	LT1001MJ8
LP5900SD- 3.3/NOPB	LPC660AMJ/883	LPR201PC10	LT1002ACJ
	LPC660IM	LPR201PC12	LT1002ACN
LP5900TL- 1.5/NOPB	LPC661AIM	LPR201PC15	LT1002AMJ
	LPC661AIN	LPR201PC20	LT1002CJ
LP5900TL- 2.8/NOPB	LPC661AMN	LPV321M5	LT1002CN
LP5900TL- 3.3/NOPB	LPC661IM	LPV321M7	LT1002MJ
	LPC661IN	LPV324M	LT1006ACH
LP5900XRX- 2.8/NOPB	LPC662AIM	LPV324MT	LT1006ACJ8
	LPC662AIN	LPV358MM	LT1006AMH
LP5907MFX- 1.5/NOPB	LPC662AMD	LPV358MX	LT1006AMJ8
LP5907MFX- 2.85/NOPB	LPC662AMJ/883	LPV511MG	LT1006CH
	LPC662IM	LPV521MG	LT1006CJ8
LP5907MFX- 3.2/NOPB	LPC662IN	LPV542DNXR	LT1006CN8
	LPR200JC10	LT1001	LT1006MH

Multisim 14.1 Base Edition Components

LT1006MJ8	LT1008S8	LT1013AMP	LT1016CN8
LT1006S8	LT1010CDD	LT1013CH	LT1016CS8
LT1007ACH	LT1010CH	LT1013CJ8	LT1016IN8
LT1007ACJ8	LT1010CN8	LT1013CN8	LT1016IS8
LT1007ACN8	LT1010CT	LT1013CP	LT1017CN8
LT1007ACP	LT1010MH	LT1013DD	LT1017CS8
LT1007AMH	LT1011CN8	LT1013DID	LT1017CSW
LT1007AMJ8	LT1011CS8	LT1013DIP	LT1018CN8
LT1007AMJG	LT1012	LT1013DMD	LT1018CS8
LT1007AML	LT1012ACH	LT1013DMJG	LT1018CSW
LT1007AMP	LT1012ACN8	LT1013DMP	LT1021BCH-5
LT1007CDW	LT1012AMH	LT1013DN8	LT1021BCN8-10
LT1007CH	LT1012CH	LT1013DP	LT1021BCN8-5
LT1007CJ8	LT1012CN8	LT1013IP	LT1021BCN8-7
LT1007CN8	LT1012DH	LT1013MFK	LT1021BMH-10
LT1007CP	LT1012DN8	LT1013MH	LT1021DCS8-10
LT1007CS	LT1012MH	LT1013MJ8	LT1021DCS8-5
LT1007MH	LT1012S8	LT1013MJG	LT1021DCS8-7
LT1007MJ8	LT1013ACH	LT1013MP	LT1022ACH
LT1007MJG	LT1013ACJ8	LT1014ACJ	LT1022AMH
LT1007ML	LT1013ACP	LT1014AMJ	LT1022CH
LT1007MP	LT1013AIP	LT1014CJ	LT1022CN8
LT1008CH	LT1013AMFK	LT1014CN	LT1022MH
LT1008CN8	LT1013AMH	LT1014DN	LT1024ACN
LT1008MH	LT1013AMJ8	LT1014MJ	LT1024AMD

Multisim 14.1 Base Edition Components

LT1024CN	LT1037CJ8	LT1057AMJ8	LT1077MH
LT1024MD	LT1037CN8	LT1057CH	LT1077MJ8
LT1028	LT1037CP	LT1057CJ8	LT1077S8
LT1028ACH	LT1037CS	LT1057CN8	LT1078ACH
LT1028ACJ8	LT1037MH	LT1057IS	LT1078ACN8
LT1028ACN8	LT1037MJ8	LT1057MH	LT1078AMJ8
LT1028AMH	LT1037MJG	LT1057MJ8	LT1078CN8
LT1028AMJ8	LT1037ML	LT1057S	LT1078IN8
LT1028CH	LT1037MP	LT1058ACJ	LT1078IS8
LT1028CJ8	LT1055ACH	LT1058ACN	LT1078MH
LT1028CN8	LT1055AMH	LT1058AMJ	LT1078MJ8
LT1028CS	LT1055CH	LT1058CJ	LT1078S8
LT1028MH	LT1055CN8	LT1058CMJ	LT1079ACN
LT1028MJ8	LT1055MH	LT1058CN	LT1079AM
LT1037ACH	LT1055S8	LT1077ACH	LT1079CN
LT1037ACJ8	LT1056ACH	LT1077ACJ8	LT1079IN
LT1037ACN8	LT1056AMH	LT1077ACN8	LT1079ISW
LT1037ACP	LT1056CH	LT1077AIN8	LT1079MJ
LT1037AMH	LT1056CN8	LT1077AMH	LT1079SW
LT1037AMJ8	LT1056MH	LT1077AMJ8	LT1083CP
LT1037AMJG	LT1056S8	LT1077CH	LT1084CP
LT1037AML	LT1057ACH	LT1077CJ8	LT1084CT
LT1037AMP	LT1057ACJ8	LT1077CN8	LT1085CM
LT1037CDW	LT1057ACN8	LT1077IN8	LT1085CT
LT1037CH	LT1057AMH	LT1077IS8	LT1097CN8

Multisim 14.1 Base Edition Components

LT1097S8	LT1121CN8	LT1128CS8	LT1179CJ
LT1101ACH	LT1121CS8	LT1129CQ	LT1179CN
LT1101ACJ8	LT1122ACJ8	LT1129CS8	LT1179IN
LT1101ACN8	LT1122ACN8	LT1129CT	LT1179MJ
LT1101AIN8	LT1122AMJ8	LT1167CN8	LT1179S
LT1101AMH	LT1122BCJ8	LT1167CS8	LT1179SW
LT1101AMJ8	LT1122BCN8	LT1168CN8	LT1187CJ8
LT1101CH	LT1122BMJ8	LT1168CS8	LT1187CN8
LT1101CJ8	LT1122CCJ8	LT1169CN8	LT1187CS8
LT1101CN8	LT1122CCN8	LT1169CS8	LT1187MJ8
LT1101IN8	LT1122CMJ8	LT1178ACH	LT1189CJ8
LT1101MH	LT1122CS8	LT1178ACJ8	LT1189CN8
LT1101MJ8	LT1122DCJ8	LT1178ACN8	LT1189CS8
LT1101S	LT1122DCN8	LT1178AMH	LT1189MJ8
LT1102ACN8	LT1122DMJ8	LT1178AMJ8	LT118AH
LT1102CN8	LT1122DS8	LT1178CH	LT118AJ8
LT1102IN8	LT1124CN8	LT1178CJ8	LT1190CJ8
LT1112S8	LT1124CS8	LT1178CN8	LT1190CN8
LT1113ACN8	LT1125CN	LT1178IN8	LT1190CS8
LT1113CS8	LT1125CSW	LT1178MH	LT1190MJ8
LT1114S	LT1126CN8	LT1178MJ8	LT1191CJ8
LT1115CN8	LT1126CS8	LT1178S	LT1191CN8
LT1115CS	LT1127CN	LT1179ACJ	LT1191CS8
LT1116CN8	LT1127CSW	LT1179ACN	LT1191MJ8
LT1116CS8	LT1128CN8	LT1179AMJ	LT1192CJ8

Multisim 14.1 Base Edition Components

LT1192CN8	LT1208CN8	LT1215MJ8	LT1226CN8
LT1192CS8	LT1208CS8	LT1216CN	LT1226CS8
LT1192MJ8	LT1209CN	LT1216CS	LT1227CN8
LT1193CJ8	LT1209CS	LT1217CN8	LT1227CS8
LT1193CN8	LT1210CR	LT1217CS8	LT1227MJ8
LT1193CS8	LT1210CS	LT1218CN8	LT1228CN8
LT1193MJ8	LT1210CT7	LT1218CS8	LT1228CS8
LT1194CJ8	LT1211ACN8	LT1219CN8	LT1229CJ8
LT1194CN8	LT1211AMJ8	LT1219CS8	LT1229CN8
LT1194CS8	LT1211CN8	LT1220CN8	LT1229CS8
LT1194MJ8	LT1211CS8	LT1220CS8	LT1229MJ8
LT1195CJ8	LT1211MJ8	LT1220MJ8	LT1230CJ
LT1195CN8	LT1212CN	LT1221CN8	LT1230CN
LT1195CS8	LT1212CS	LT1221CS8	LT1230CS
LT1195MJ8	LT1213ACN8	LT1221MJ8	LT1230MJ
LT1200	LT1213AMJ8	LT1222CN8	LT1251CN
LT1201CN8	LT1213CN8	LT1222IS8	LT1251CS
LT1201CS8	LT1213CS8	LT1223CJ8	LT1252CN8
LT1202CN	LT1213MJ8	LT1223CN8	LT1252CS8
LT1202CS	LT1214CN	LT1223CS8	LT1253CN8
LT1206CN8	LT1214CS	LT1223MJ8	LT1253CS8
LT1206CR	LT1215ACN8	LT1224CN8	LT1254CN
LT1206CS8	LT1215AMJ8	LT1224CS8	LT1254CS
LT1206CY	LT1215CN8	LT1225CN8	LT1256CN
LT1207CS	LT1215CS8	LT1225CS8	LT1256CS

Multisim 14.1 Base Edition Components

LT1259CN	LT1360CN8	LT1397CGN	LT1466LCN8
LT1259CS	LT1360CS8	LT1397CS	LT1466LCS8
LT1260CN	LT1361CN8	LT1398CS	LT1467LCS
LT1260CS	LT1361CS8	LT1399CGN	LT1468CDD
LT1328CMS8	LT1362CN	LT1399CS	LT1468CN8
LT1328CS8	LT1362CS	LT1413ACN8	LT1468CS8
LT1351CMS8	LT1363CN8	LT1413CN8	LT1468IDD
LT1351CN8	LT1363CS8	LT1413S8	LT1468IN8
LT1351CS8	LT1364CN8	LT1431CN8	LT1468IS8
LT1352CN8	LT1364CS8	LT1431CS8	LT1469CN8
LT1352CS8	LT1365CN	LT1457CN8	LT1469CS8
LT1353CS	LT1365CS	LT1457S8	LT1490CMS8
LT1354CN8	LT1366CN8	LT1461-25	LT1490CN8
LT1354CS8	LT1366CS8	LT1461-3	LT1490CS8
LT1355CN8	LT1367CS	LT1461-33	LT1491CN
LT1355CS8	LT1368CN8	LT1461-4	LT1491CS
LT1356CN	LT1368CS8	LT1461-5	LT1492CN8
LT1356CS	LT1369CS	LT1462CN8	LT1492CS8
LT1357CN8	LT1394CMS8	LT1462CS8	LT1493CS
LT1357CS8	LT1395CS5	LT1463CN	LT1494CMS8
LT1358CN8	LT1395CS6	LT1463CS	LT1494CN8
LT1358CS8	LT1395CS8	LT1464CN8	LT1494CS8
LT1359CN	LT1396CDD	LT1464CS8	LT1495CN8
LT1359CS	LT1396CMS8	LT1465CN	LT1495CS8
LT1359CS14	LT1396CS8	LT1465CS	LT1496CN

Multisim 14.1 Base Edition Components

LT1496CS	LT1637CMS8	LT1677CN8	LT1724CS
LT1497CS	LT1637CN8	LT1677CS8	LT1739CFE
LT1497CS8	LT1637CS8	LT1678CS8	LT1739CUE
LT1498CN8	LT1638CDD	LT1679CS	LT1739IFE
LT1498CS8	LT1638CMS8	LT1711CMS8	LT1739IUE
LT1499CS	LT1638CN8	LT1712CGN	LT1761ES5-1.8
LT1521CMS8	LT1638CS8	LT1713CMS8	LT1761ES5-2
LT1521CS8	LT1639CN	LT1714CGN	LT1761ES5-2.5
LT1529CQ	LT1639CS	LT1715CMS	LT1761ES5-3
LT1529CT	LT1671CMS8	LT1716CS5	LT1761ES5-3.3
LT1568CGN	LT1671CS8	LT1719CS8	LT1761ES5-5
LT1568IGN	LT1672CMS8	LT1719IS8	LT1761ES5-BYP
LT1630CN8	LT1672CN8	LT1720CDD	LT1761ES5-SD
LT1630CS8	LT1672CS8	LT1720CMS8	LT1762EMS8
LT1631CS	LT1672IMS8	LT1720CS8	LT1762EMS8-2.5
LT1632CN8	LT1672IN8	LT1720IDD	LT1762EMS8-3
LT1632CS8	LT1672IS8	LT1720IMS8	LT1762EMS8-3.3
LT1633CS	LT1673CN8	LT1720IS8	LT1762EMS8-5
LT1635CN8	LT1673CS8	LT1721CGN	LT1763CDE
LT1635CS8	LT1673IN8	LT1721CS	LT1763CDE-1.5
LT1636CDD	LT1673IS8	LT1721IGN	LT1763CDE-1.8
LT1636CMS8	LT1674CN	LT1722CS5	LT1763CDE-2.5
LT1636CN8	LT1674CS	LT1722CS8	LT1763CDE-3
LT1636CS8	LT1674IN	LT1723CMS8	LT1763CDE-3.3
LT1637CDD	LT1674IS	LT1723CS8	LT1763CDE-5

Multisim 14.1 Base Edition Components

LT1763CS8	LT1789CS8-1	LT1806CS8	LT1816CS8
LT1763CS8-1.5	LT1789CS8-10	LT1807CMS8	LT1816IDD
LT1763CS8-1.8	LT1790ACS6-1.25	LT1807CS8	LT1816IMS8
LT1763CS8-2.5	LT1790ACS6-2.048	LT1809CS6	LT1816IS8
LT1763CS8-3	LT1790ACS6-2.5	LT1809CS8	LT1817CGN
LT1763CS8-3.3	LT1790ACS6-3	LT1810CMS8	LT1817CS
LT1763CS8-5	LT1790ACS6-3.3	LT1810CS8	LT1817IGN
LT1763IS8	LT1790ACS6-4.096	LT1812CS5	LT1817IS
LT1763IS8-1.5	LT1790ACS6-5	LT1812CS6	LT1818CS5
LT1763IS8-1.8	LT1792CN8	LT1812CS8	LT1818CS8
LT1764EFE	LT1792CS8	LT1813CDD	LT1818IS5
LT1764EFE-1.5	LT1793CN8	LT1813CS8	LT1818IS8
LT1764EFE-1.8	LT1793CS8	LT1813DMS8	LT1819CMS8
LT1764EFE-2.5	LT1794CFE	LT1814CGN	LT1819CS8
LT1764EFE-3.3	LT1794CSW	LT1814CS	LT1819IMS8
LT1764EQ	LT1795CFE	LT1815CS5	LT1819IS8
LT1764EQ-1.5	LT1795CSW	LT1815CS6	LT1880CS5
LT1764EQ-1.8	LT1797CS5	LT1815CS8	LT1881CN8
LT1764EQ-2.5	LT1800CS5	LT1815IS5	LT1881CS8
LT1764EQ-3.3	LT1800CS8	LT1815IS6	LT1882CS
LT1782CS6	LT1801CDD	LT1815IS8	LT1884CN8
LT1783CS6	LT1801CMS8	LT1816ACMS	LT1884CS8
LT1784CS6	LT1801CS8	LT1816AIMS	LT1885CS
LT1784IS6	LT1802CS	LT1816CDD	LT1886CS8
LT1787CMS8	LT1806CS6	LT1816CMS8	LT1920CN8

Multisim 14.1 Base Edition Components

LT1920CS8	LT1995IMS	LT6003CDC	LT6100CDD
LT1962EMS8	LT1996CDD	LT6003CS5	LT6100CMS8
LT1962EMS8-1.5	LT1996CMS	LT6003HDC	LT6200CS6
LT1962EMS8-1.8	LT2078ACS8	LT6003HS5	LT6200CS6-10
LT1962EMS8-2.5	LT2078AIS8	LT6003IDC	LT6200CS6-5
LT1962EMS8-3	LT2078CS8	LT6003IS5	LT6200CS8
LT1962EMS8-3.3	LT2079ACS	LT6004CDD	LT6200CS8-10
LT1962EMS8-5	LT2079CS	LT6004CMS8	LT6200CS8-5
LT1963EFE	LT2178ACS8	LT6004HDD	LT6201CDD
LT1963EFE-1.5	LT2178CS8	LT6004HMS8	LT6201CS8
LT1963EFE-1.8	LT2179ACS	LT6004IDD	LT6202CS5
LT1963EFE-2.5	LT2179CS	LT6004IMS8	LT6202CS8
LT1963EFE-3.3	LT318A	LT6005CDHC	LT6203CDD
LT1970CFE	LT318AJ8	LT6005CGN	LT6203CMS8
LT1990CS8	LT318AN8	LT6005HDHC	LT6203CS8
LT1991CDD	LT6000CDCB	LT6005HGN	LT6204CGN
LT1991CMS	LT6000IDCB	LT6005IDHC	LT6204CS
LT1993CUD-10	LT6001CDD	LT6005IGN	LT6205CS5
LT1993CUD-2	LT6001CMS8	LT6010CDD	LT6206CMS8
LT1993CUD-4	LT6001IDD	LT6010CS8	LT6207CGN
LT1994CDD	LT6001IMS8	LT6011CDD	LT6220CS5
LT1994CMS8	LT6002CDHC	LT6011CMS8	LT6220CS8
LT1995CDD	LT6002CGN	LT6011CS8	LT6221CDD
LT1995CMS	LT6002IDHC	LT6012CGN	LT6221CS8
LT1995IDD	LT6002IGN	LT6012CS	LT6222CGN

Multisim 14.1 Base Edition Components

LT6230CS6	LT6557IDHC	LTC1050ACH	LTC1053CN
LT6231CDD	LT6557IGN	LTC1050ACJ8	LTC1053CS
LT6231CS8	LT6558CDHC	LTC1050ACN	LTC1053CSW
LT6232CGN	LT6558CGN	LTC1050ACN8	LTC1100CN8
LT6233CS6	LT6558IDHC	LTC1050AMH	LTC1100CSW
LT6234CDD	LT6558IGN	LTC1050AMJ8	LTC1150CJ8
LT6234CS8	LT6559CUD	LTC1050CH	LTC1150CN8
LT6235CGN	LT6600-10	LTC1050CJ8	LTC1150CS8
LT6235IGN	LT6600-2.5	LTC1050CN	LTC1150MJ8
LT6402CUD-12	LT6600-20	LTC1050CN8	LTC1151CN8
LT6402CUD-20	LT6600-5	LTC1050MH	LTC1151CSW
LT6402CUD-6	LT6650CS5	LTC1050MJ8	LTC1152CN8
LT6402IUD-12	LT6700CDCB-1	LTC1051ACJ8	LTC1152CS8
LT6402IUD-20	LT6700CDCB-2	LTC1051ACN8	LTC1250CN8
LT6402IUD-6	LT6700CDCB-3	LTC1051ACS	LTC1250CS8
LT6411CUD	LT6700CS6-1	LTC1051AMJ8	LTC1440CDD
LT6411IUD	LT6700CS6-2	LTC1051CJ8	LTC1440CMS8
LT6552CDD	LT6700CS6-3	LTC1051CN8	LTC1440CN8
LT6552CS8	LTC1043CN	LTC1051CS	LTC1440CS8
LT6552IDD	LTC1043CSW	LTC1051MJ8	LTC1441CN8
LT6552IS8	LTC1047CN8	LTC1052CD	LTC1441CS8
LT6553CGN	LTC1047CS	LTC1052CP	LTC1442CN8
LT6553IGN	LTC1049CJ8	LTC1052CS	LTC1442CS8
LT6557CDHC	LTC1049CN8	LTC1052MD	LTC1443CDHD
LT6557CGN	LTC1049CS8	LTC1052MP	LTC1443CN

Multisim 14.1 Base Edition Components

LTC1443CS	LTC1798CS8-4.1	LTC6101ACMS8	LTC6910-1CTS8
LTC1444CDHD	LTC1798CS8-5	LTC6101BCS5	LTC6910-2CTS8
LTC1444CN	LTC1841CS8	LTC6240CS5	LTC6910-3CTS8
LTC1444CS	LTC1842CS8	LTC6240CS8	LTC6911CMS-1
LTC1444IDHD	LTC1966CMS8	LTC6240HS5	LTC6911CMS-2
LTC1444IN	LTC1967CMS8	LTC6240HS8	LTC7652CH
LTC1444IS	LTC1968CMS8	LTC6240IS5	LTR-516AD
LTC1445CDHD	LTC2050CS5	LTC6240IS8	LVL_BARGRAPH
LTC1445CN	LTC2050CS6	LTC6241CDD	LVM_CURRENT
LTC1445CS	LTC2050CS8	LTC6241CS8	LVM_VOLTAGE
LTC152	LTC2051CMS10	LTC6241HS8	LVT22V10-7A
LTC1540CDD	LTC2052CGN	LTC6241IDD	LVT22V10-7N
LTC1540CMS8	LTC2052CS	LTC6241IS8	LVT22V10B7A
LTC1540CS8	LTC2053CDD	LTC6242CDHC	M37702S1AFP
LTC1541CDD	LTC2053CMS8	LTC6242CGN	M37702S1BFP
LTC1541CMS8	LTC2053HDD	LTC6242HGN	M6060P-E3/45
LTC1541CS8	LTC2053HMS8	LTC6242IDHC	M68AF031AL_SO28
LTC1542CDD	LTC2053IMS8-SYNC	LTC6242IGN	M68AF127BL_SO32
LTC1542CMS8	LTC2054CS5	LTC6244CDD	M68AF511AL_SO32
LTC1542CS8	LTC2055CDD	LTC6244CMS8	M68AW031AL_SO28
LTC1563-2CGN	LTC2055CMS8	LTC6244HMS8	M68AW064FL_FBG A48
LTC1563-3CGN	LTC6078CDD	LTC6244IDD	M68AW128ML_SO44
LTC1798CS8	LTC6078CMS8	LTC6244IMS8	
LTC1798CS8-2.5	LTC6079CDHC	LTC6800HDD	
LTC1798CS8-3	LTC6079CGN	LTC6800HMS8	

Multisim 14.1 Base Edition Components

M68AW256ML_SO 44	MAC212-10	MAC228-6	MAX1184_FP48
	MAC212-4	MAC228-8	MAX1185_FP48
M68AW511AL_SO3 2	MAC212-6	MAC228A-10	MAX1195_FP48
M68AW512DL_FBG A48	MAC212-8	MAC228A-4	MAX1197_FP48
	MAC212A-10	MAC228A-6	MAX1198_FP48
M68AW512ML_SO 44	MAC212A-4	MAC228A-8	MAX1284_SO8
MAC08MT1G	MAC212A-6	MAC23A-10	MAX1285_SO8
MAC12HCDG	MAC212A-8	MAG_CMP4	MAX1290_SO28
MAC15-10	MAC223-10	MAG_OL	MAX1291_SO28
MAC15-4	MAC223-4	MAG_OL_RELAY	MAX1292_SO24
MAC15-6	MAC223-6	MAGNETIC_CORE_ VIRTUAL	MAX1293_SO24
MAC15-8	MAC223-8		MAX1420_FP48
	MAC223A-4	MAT02EH	MAX1421_FP48
MAC15A-10	MAC223A-6	MAT02FH	MAX1422_FP48
MAC15A-4	MAC223A-8	MAT03EH	MAX1444_FP32
MAC15A-6	MAC224-10	MAT03FH	MAX1446_FP32
MAC15A-8	MAC224-4	MAT04AY	MAX1449_FP32
MAC210-10	MAC224-6	MAT04EY	MAX15006AASA+
MAC210-4	MAC224-8	MAT04FP	MAX15006AATT+
MAC210-6	MAC224A-10	MAT04FS	MAX15007AASA+
MAC210-8	MAC224A-4	MAT04FY	MAX15007AATT+
MAC210A-10	MAC224A-6	MAX1180_FP48	MAX16814AGP/VY+
MAC210A-4	MAC224A-8	MAX1181_FP48	MAX16814ATP+
MAC210A-6	MAC228-10	MAX1182_FP48	MAX16814AUP+
MAC210A-8	MAC228-4	MAX1183_FP48	MAX16820ATT+

Multisim 14.1 Base Edition Components

MAX16823ATE+	MAX274ACWI	MAX4032EUT+	MAX406BESA+
MAX16823AUE+	MAX274BCNG	MAX4032EXT+	MAX406BMJA
MAX16826AGJ/VY+	MAX274BCWI	MAX4036AAXK+	MAX4070ATA+
MAX16826ATJ+	MAX280_SO16	MAX4036EXK+	MAX4070AUA+
MAX16832AASA+	MAX281A_SO16	MAX4037EUT+	MAX4071ATA+
MAX16832CASA+	MAX291_SO16	MAX4038AAUA+	MAX4071AUA+
MAX16833AUE+	MAX292_SO16	MAX4038EBL+T	MAX4072ATA+
MAX16834AGP/VY+	MAX295_SO16	MAX4038ETA+	MAX4072AUA+
MAX16834ATP+	MAX296_SO16	MAX4038EUA+	MAX4073TAUT+
MAX16834AUP+	MAX4004EUT+	MAX4039EBL+T	MAX4073TAXK+
MAX16838ATP+	MAX4006EUT+	MAX4039ETB+T	MAX407CPA+
MAX16838AUP+	MAX4007EUT+	MAX4039EUB+	MAX407CSA+
MAX16839ASA+	MAX4008EUT+	MAX403CPA	MAX407EPA+
MAX16839ATT+	MAX4012ESA+	MAX403CSA	MAX407ESA+
MAX1966_SO8	MAX4012EUK+	MAX403EPA	MAX407MJA
MAX1967_SO10	MAX4016ESA+	MAX403ESA	MAX4080FASA+
MAX209ENG	MAX4016EUA+	MAX4069AUB+	MAX4080FAUA+
MAX213EAI	MAX4018EEE+	MAX406ACPA+	MAX4080SASA+
MAX218CPP	MAX4018ESD+	MAX406ACSA+	MAX4080SAUA+
MAX263_DIP28	MAX4020EEE+	MAX406AEPA+	MAX4080TASA+
MAX264_DIP28	MAX4020ESD+	MAX406AESA+	MAX4080TAUA+
MAX267_DIP24	MAX402CPA	MAX406AMJA	MAX4081FASA+
MAX268_DIP24	MAX402CSA	MAX406BCPA+	MAX4081FAUA+
MAX2740ECM	MAX402EPA	MAX406BCSA+	MAX4081SASA+
MAX274ACNG	MAX402ESA	MAX406BEPA+	MAX4081SAUA+

Multisim 14.1 Base Edition Components

MAX4081TASA+	MAX4100ESA+	MAX410EPA	MAX412BESA
MAX4081TAUA+	MAX4100EUA+	MAX410EPA+	MAX412BESA+
MAX4090AALT+T	MAX4101ESA	MAX410ESA+	MAX412CPA
MAX4090AAUT+	MAX4101ESA+	MAX410ETA-T	MAX412CPA+
MAX4090AAXT+	MAX4104ESA	MAX4112ESA+	MAX412CSA
MAX4090ELT+T	MAX4104ESA+	MAX4112EUA	MAX412CSA+
MAX4090EUT+	MAX4104EUK+	MAX4113ESA+	MAX412EPA
MAX4090EXT+	MAX4105ESA+	MAX4117ESA+	MAX412EPA+
MAX4091ASA+	MAX4105EUK+T	MAX4118ESA+	MAX412ESA
MAX4091AUA+	MAX4106ESA	MAX4119EEE	MAX412ESA+
MAX4091AUK+	MAX4106ESA+	MAX4119ESD+	MAX412MJA
MAX4092ASA+	MAX4107ESA	MAX4120ESD+	MAX4130EUK+
MAX4092AUA+	MAX4107ESA+	MAX4122EUK+	MAX4131EBT+
MAX4094ASD+	MAX4108ESA	MAX4124EUK+	MAX4131ESA+
MAX4094AUD+	MAX4108ESA+	MAX4126ESA+	MAX4131EUA+
MAX409ACPA+	MAX4109ESA+	MAX4126EUA+	MAX4132ESA+
MAX409ACSA+	MAX410BCPA	MAX4128ESA+	MAX4132EUA+
MAX409AEPA	MAX410BCSA	MAX4128EUA+	MAX4133ESD
MAX409AESA+	MAX410BCSA+	MAX4129ESD+	MAX4134ESD+
MAX409AMJA	MAX410BEPA	MAX412BCPA	MAX414BCPD
MAX409BCPA+	MAX410BESA	MAX412BCPA+	MAX414BCSD
MAX409BCSA+	MAX410CPA	MAX412BCSA	MAX414BCSD+
MAX409BEPA+	MAX410CPA+	MAX412BCSA+	MAX414BEPD
MAX409BESA+	MAX410CSA	MAX412BEPA	MAX414BESD
MAX4100ESA	MAX410CSA+	MAX412BEPA+	MAX414BESD+

Multisim 14.1 Base Edition Components

MAX414CPD	MAX4169EPD	MAX4186ESD+	MAX419ESD+
MAX414CPD+	MAX4169ESD+	MAX4187EEE+	MAX419MJD
MAX414CSD	MAX4172EUA+	MAX4187ESD+	MAX4200ESA+
MAX414CSD+	MAX4173TESA+	MAX4188EEE+	MAX4200EUK+
MAX414EPD	MAX4173TEUT+	MAX4188ESD+	MAX4201ESA+
MAX414EPD+	MAX4178EPA+	MAX4189EEE+	MAX4201EUK+T
MAX414ESD	MAX4178ESA+	MAX4189ESD+	MAX4202ESA+
MAX414ESD+	MAX4178EUA+	MAX418CPD+	MAX4202EUK+T
MAX414MJD	MAX4178EUK+T	MAX418CSD+	MAX4203ESA+
MAX4162ESA+	MAX4178MJA	MAX418EPD+	MAX4203EUA+
MAX4162EUK+	MAX417CPA+	MAX418ESD+	MAX4204ESA+
MAX4163EBL+	MAX417CSA+	MAX418MJD	MAX4204EUA+
MAX4163ESA+	MAX417EPA+	MAX4190ESA+	MAX4205ESA
MAX4163EUA+	MAX417ESA+	MAX4190EUA	MAX4205EUA+
MAX4164ESD+	MAX417MJA	MAX4194ESA+	MAX4206ETE
MAX4165EUK+	MAX4180ESA+	MAX4195ESA+	MAX4212EUK+
MAX4166ELA+	MAX4180EUT+T	MAX4196ESA+	MAX4213ESA+
MAX4166EPA+	MAX4181ESA+	MAX4197ESA+	MAX4213EUA+
MAX4166ESA+	MAX4181EUT+T	MAX4198ESA+	MAX4214EUK+
MAX4166EUA+	MAX4182ESA+	MAX4198EUA+	MAX4215ESA+
MAX4167EPA+	MAX4183ESD+	MAX4199ESA+	MAX4215EUA+
MAX4167ESA+	MAX4183EUB+	MAX4199EUA+	MAX4216ESA+
MAX4168EPD+	MAX4184ESA+	MAX419CPD+	MAX4216EUA+
MAX4168ESD+	MAX4185ESD	MAX419CSD+	MAX4217ESA+
MAX4168EUB+	MAX4185EUB+	MAX419EPD+	MAX4217EUA+

Multisim 14.1 Base Edition Components

MAX4218EEE+	MAX4232AUA+	MAX4242EUA+	MAX4265ESA+
MAX4218ESD+	MAX4233ABC+T	MAX4243ESD	MAX4265EUA+
MAX4219EEE+	MAX4233AUB+	MAX4243EUB+	MAX4266ESA+
MAX4219ESD+	MAX4234ASD+	MAX4244ESD+	MAX4266EUA+
MAX4220EEE+	MAX4234AUD+	MAX4245AUT+	MAX4267ESA+
MAX4220ESD+	MAX4236AESA+	MAX4245AXT+	MAX4267EUA
MAX4222EEE+	MAX4236AEUA	MAX4247AUB+	MAX4268EEE+
MAX4222ESD+	MAX4236BESA+	MAX4249ESD+	MAX4268ESD+
MAX4223ESA+	MAX4236BEUA+	MAX4249EUB+	MAX4269EEE
MAX4223EUT+	MAX4236EUT+	MAX4250AAUK+	MAX4269ESD
MAX4224ESA+	MAX4237AESA+	MAX4250EUK+	MAX4270EEE
MAX4224EUT+	MAX4237AEUA+	MAX4251ESA+	MAX4270ESD
MAX4225ESA+	MAX4237BESA+	MAX4251EUA+	MAX4278EPA+
MAX4226ESD	MAX4237BEUA+	MAX4252EBL+	MAX4278ESA+
MAX4226EUB+	MAX4237EUT+	MAX4252ESA+	MAX4278EUA+
MAX4227ESA+	MAX4238ASA+	MAX4252EUA+	MAX4278EUK+
MAX4228ESD+	MAX4238ATT+	MAX4253EBC+	MAX4278MJA
MAX4228EUB+	MAX4238AUT+	MAX4253ESD+	MAX427CPA+
MAX4230AUK+	MAX4239ASA+	MAX4253EUB+	MAX427CSA+
MAX4230AXK+	MAX4239ATT+	MAX4254ESD+	MAX427EPA+
MAX4231ART+T	MAX4239AUT+	MAX4255EUK+	MAX427ESA+
MAX4231AUT+	MAX4240EUK+	MAX4256ESA+	MAX427MJA
MAX4231AXT+	MAX4241ESA+	MAX4256EUA+	MAX4281ESA+
MAX4231AYT+	MAX4241EUA+	MAX4257ESA+	MAX4281EUK+
MAX4232AKA+	MAX4242ESA+	MAX4257EUA+	MAX4282ESA+

Multisim 14.1 Base Edition Components

MAX4282EUA+	MAX4323EUT+	MAX436CSD+	MAX4374TEUB+
MAX4284EEE	MAX4327ESD	MAX436EPD	MAX4375FESD+
MAX4284ESD	MAX4327EUB+	MAX436ESD	MAX4375FEUB+
MAX4285ESA+	MAX4330EUK+	MAX436ESD+	MAX4375HESD+
MAX4285EUT+	MAX4331ESA+	MAX436MJD	MAX4375HEUB+
MAX4286ESA+	MAX4331EUA+	MAX4372FEBT+T	MAX4375TESD+
MAX4286EUT-T	MAX4332ESA+	MAX4372FESA+	MAX4375TEUB+
MAX4288ESD	MAX4333ESD+	MAX4372FEUK+	MAX4376FASA+T
MAX4288EUB	MAX4333EUB+	MAX4372HEBT+T	MAX4376FAUK+T
MAX4289ESA+	MAX4334ESD+	MAX4372HESA+	MAX4376HASA+T
MAX4289EUT+	MAX4335EXT+	MAX4372HEUK+	MAX4376HAUK+T
MAX4291EUK+	MAX4336EUT-T	MAX4372TEBT+T	MAX4376TASA+T
MAX4291EXK+	MAX4336EXT+	MAX4372TESA+	MAX4376TAUK+T
MAX4292EBL+	MAX4337EKA+	MAX4372TEUK+	MAX437CPA
MAX4292ESA+	MAX4337EUA+	MAX4373FESA+	MAX437CSA+
MAX4292EUA+	MAX4338EUB+	MAX4373FEUA+	MAX437EPA
MAX4294ESD+	MAX435CPD	MAX4373HESA+	MAX437ESA+
MAX4294EUD+	MAX435CSD	MAX4373HEUA+	MAX437MJA
MAX4304ESA+	MAX435CSD+	MAX4373TESA+	MAX4380EUT+
MAX4304EUK+	MAX435EPD	MAX4373TEUA+	MAX4380EXT+
MAX4305ESA+	MAX435ESD	MAX4374FESD+	MAX4381EUB+
MAX4305EUK+	MAX435ESD+	MAX4374FEUB+	MAX4382EEE+
MAX4323EBT+T	MAX435MJD	MAX4374HESD+	MAX4382ESD+
MAX4323ESA+	MAX436CPD	MAX4374HEUB+	MAX4382EUD+
MAX4323EUA	MAX436CSD	MAX4374TESD+	MAX4383EEE+

Multisim 14.1 Base Edition Components

MAX4383ESD+	MAX4402ASA+	MAX44243ASD+	MAX44281UANS+
MAX4383ESE+	MAX4402AUA+	MAX44243AUD+	MAX44281VANS+
MAX4383EUD+	MAX4403ASD+	MAX44244AUA+	MAX44284EAUT+
MAX4384EUP+	MAX4403AUD+	MAX44244AUK+	MAX44284EAWT+
MAX4385EEUK+	MAX4412EUK+	MAX44245ASD+	MAX44284FAUT+
MAX4386EESD+	MAX4412EXK+	MAX44245AUD+	MAX44284FAWT+
MAX4386EEUD+	MAX4413EKA+	MAX44246ASA+	MAX44284HAUT+
MAX4388ESD+	MAX4414ESA+	MAX44246AUA+	MAX44284HAWT+
MAX4388EUB	MAX4414EUA+	MAX44248ASA+	MAX44284WAUT+
MAX4389EUT+	MAX4415ESA+	MAX44248AUA+	MAX44284WAWT+
MAX4389EXT+	MAX4415EUA+	MAX44250AUA+	MAX44285FAUA+
MAX4390EUK+	MAX4416ESA+	MAX44250AUK+	MAX44285FAWA+T
MAX4390EXT+	MAX4416EUA+	MAX44251AKA+	MAX44285HAUA+
MAX4392ESA+	MAX4417ESA+	MAX44251AUA+	MAX44285HAWA+T
MAX4392EUA+	MAX4417EUA+	MAX44252ASD+	MAX44285LAUA+
MAX4393EUB+	MAX4418EUD+	MAX44260AXT+	MAX44285LAWA+T
MAX4394ESD+	MAX4419EUD+	MAX44260AYT+	MAX44285TAUA+
MAX4394EUD+	MAX44205ATC+	MAX44263AXA+	MAX44285TAWA+T
MAX4395ESD+	MAX44205AUB+	MAX44264EWT+	MAX44286FAZS+T
MAX4395EUD+	MAX44206AUA+	MAX44265EWT+	MAX44286HAZS+T
MAX4396EUP+	MAX44211ETP+T	MAX44267AUD+	MAX44286TAZS+T
MAX4400AUK+	MAX44241AUA+	MAX44269EWL+	MAX44286WAZS+T
MAX4400AXK+	MAX44241AUK+T	MAX44280AXT+	MAX44291AUA+
MAX4401AXT+	MAX44242AKA+	MAX44280AYT+	MAX44292ASA+T
MAX4402AKA+	MAX44242AUA+	MAX44281OANS+	MAX44294ASD+T

Multisim 14.1 Base Edition Components

MAX4430ESA+	MAX4461HESA+	MAX4475AUT+	MAX4488AUA+
MAX4430EUK+	MAX4461HETT+T	MAX4476ATT+T	MAX4488AUT+
MAX4432ESA	MAX4461HEUT+	MAX4476AUT+	MAX4489ASA+
MAX4432EUA+	MAX4461TESA+	MAX4477ASA+	MAX4489AUA+
MAX4434ESA	MAX4461TETT+	MAX4477AUA+	MAX4490AUK+T
MAX4434EUK+	MAX4461TEUT	MAX4478ASD+	MAX4490AXK+
MAX4435ESA	MAX4461UESA+	MAX4478AUD+	MAX4491AKA+
MAX4435EUK	MAX4461UETT+T	MAX4480AUK+	MAX4491AUA+
MAX4436ESA	MAX4461UEUT-T	MAX4480AXK+	MAX4492ASD+
MAX4436EUA+	MAX4462HESA+	MAX4481AUT+	MAX4492AUD+
MAX4437ESA	MAX4462HETT+	MAX4481AXT+	MAX4493AUK
MAX4437EUA+	MAX4462HEUT+	MAX4482AKA+	MAX4493AXK+
MAX4450EUK+	MAX4462TESA	MAX4482ASA+	MAX4494AKA+
MAX4450EXK+	MAX4462TETT+T	MAX4482AUA+	MAX4494ASA+
MAX4451EKA+	MAX4462TEUT	MAX4483ASD+	MAX4494AUA+
MAX4451ESA+	MAX4462UESA	MAX4483AUD+	MAX4495ASD+
MAX4452EUK+	MAX4462UETT+	MAX4484AUK+	MAX4495AUD+
MAX4452EXK+	MAX4464EUK+	MAX4484AXK+	MAX473CPA
MAX4453EKA+	MAX4464EXK+	MAX4486AKA+	MAX473CPA+
MAX4453ESA+	MAX4474EKA+	MAX4486ASA+	MAX473CSA
MAX4454ESD+	MAX4474ESA+	MAX4486AUA+	MAX473CSA+
MAX4454EUD+	MAX4474EUA+	MAX4487ASD+	MAX473CUA
MAX4460ESA+	MAX4475ASA+	MAX4487AUD+	MAX473CUA+
MAX4460ETT+	MAX4475ATT+	MAX4488ASA+	MAX473EPA+
MAX4460EUT+T	MAX4475AUA+	MAX4488ATT+	MAX473ESA+

Multisim 14.1 Base Edition Components

MAX473MJA	MAX478ESA+	MAX495CUA+	MAX6070BAUT12+ T
MAX474CPA	MAX479ACPD	MAX495EPA+	MAX6070BAUT18+ T
MAX474CPA+	MAX479CPD+	MAX495ESA+	MAX6070BAUT21+ T
MAX474CSA	MAX479CSD+	MAX495MJA	MAX6070BAUT25+ T
MAX474CSA+	MAX479EPD+	MAX496CPE+	MAX6070BAUT30+ T
MAX474CUA	MAX479ESD+	MAX496CSE+	MAX6070BAUT33+ T
MAX474CUA+	MAX492CPA	MAX497CPE+	MAX6070BAUT41+ T
MAX474EPA+	MAX492CPA+	MAX497CSE+	MAX6070BAUT50+ T
MAX474ESA+	MAX492CSA	MAX5631_QFN68	MAX6126A21+T
MAX474MJA	MAX492CSA+	MAX5632_QFN68	MAX6126A25+T
MAX475CPD	MAX492EPA+	MAX5633_QFN68	MAX6126A28+T
MAX475CSD	MAX492ESA+	MAX6070AAUT12+ T	MAX6126A30+T
MAX475EPD	MAX492MJA	MAX6070AAUT18+ T	MAX6126A41+T
MAX475ESD	MAX494CPD	MAX6070AAUT21+ T	MAX6126A50+T
MAX475MJD	MAX494CPD+	MAX6070AAUT25+ T	MAX6324AUT23-T
MAX4766CETA+	MAX494CSD	MAX6070AAUT30+ T	MAX6324AUT26-T
MAX477EPA+	MAX494CSD+	MAX6070AAUT33+ T	MAX6324AUT29+T
MAX477ESA+	MAX494EPD+	MAX6070AAUT41+ T	MAX6324AUT31+T
MAX477EUA+	MAX494ESD+	MAX6070AAUT50+ T	MAX6324AUT44-T
MAX477EUK+T	MAX494MJD		MAX6324AUT46+T
MAX477MJA	MAX495CPA		
MAX478ACPA+	MAX495CPA+		
MAX478CPA+	MAX495CSA		
MAX478CSA+	MAX495CSA+		
MAX478EPA+	MAX495CUA		

Multisim 14.1 Base Edition Components

MAX6324BUT23+T	MAX6324FUT26+T	MAX706REUA+	MAX7420_SO8
MAX6324BUT26-T	MAX6324FUT29-T	MAX706RMJA	MAX7421_SO8
MAX6324BUT29+T	MAX6324FUT31-T	MAX706TCPA+	MAX7422_SO8
MAX6324BUT31-T	MAX6324FUT44-T	MAX706TCSA+	MAX7423_SO8
MAX6324BUT44-T	MAX6324FUT46+T	MAX706TCUA+	MAX7424_SO8
MAX6324BUT46+T	MAX6324GUT23-T	MAX706TEPA	MAX7425_SO8
MAX6324CUT23+T	MAX6324GUT26+T	MAX706TESA+	MAX7426_SO8
MAX6324CUT26+T	MAX6324GUT29+T	MAX706TEUA+	MAX7427_SO8
MAX6324CUT29-T	MAX6324GUT31-T	MAX706TMJA	MAX803LEXR+
MAX6324CUT31-T	MAX6324GUT44-T	MAX7400_DIP8	MAX803MEXR+
MAX6324CUT44-T	MAX6324GUT46+T	MAX7401_DIP8	MAX803REXR+
MAX6324CUT46+T	MAX6324HUT23+T	MAX7403_DIP8	MAX803SEXR+
MAX6324DUT23+T	MAX6324HUT26-T	MAX7404_DIP8	MAX803TEXR+
MAX6324DUT26+T	MAX6324HUT29+T	MAX7405_DIP8	MAX803ZEXR+
MAX6324DUT29-T	MAX6324HUT31+T	MAX7407_DIP8	MAX809JEUR+
MAX6324DUT31-T	MAX6324HUT44+T	MAX7408_SO8	MAX809LEUR+
MAX6324DUT44-T	MAX6324HUT46+T	MAX7409_SO8	MAX809LEXR+
MAX6324DUT46-T	MAX6460UT+	MAX7410_SO8	MAX809MEUR+
MAX6324EUT23+T	MAX6495ATT+	MAX7411_SO8	MAX809MEXR+
MAX6324EUT26+T	MAX6780LTA+	MAX7412_SO8	MAX809REUR+
MAX6324EUT29+	MAX706RCPA	MAX7413_SO8	MAX809REXR+
MAX6324EUT31-T	MAX706RCSA+	MAX7414_SO8	MAX809SEUR+
MAX6324EUT44-T	MAX706RCUA+	MAX7415_SO8	MAX809SEXR+
MAX6324EUT46+T	MAX706REPA	MAX7418_SO8	MAX809TEUR+
MAX6324FUT23+T	MAX706RESA+	MAX7419_SO8	MAX809TEXR+

Multisim 14.1 Base Edition Components

MAX809ZEXR+	MAX9013EUA+	MAX9077ESA+	MAX9117ESA+
MAX810LEUR+	MAX9015AEKA+	MAX9077EUA+	MAX9117EXK+
MAX810LEXR+	MAX9018AEKA+	MAX9077MSA/PR2	MAX9119EXK+
MAX810MEUR+	MAX9025EBT+T	MAX907CPA	MAX9120ESA
MAX810MEXR+	MAX9026EBT+	MAX907CPA+	MAX9120EXK+
MAX810REUR+	MAX9030AUT+	MAX907CSA	MAX912CPE
MAX810REXR+T	MAX9030AXT+	MAX907CSA+	MAX912CPE+
MAX810SEUR+	MAX9031AUK+	MAX907EPA	MAX912CSE
MAX810SEXR+	MAX9031AXK+	MAX907EPA+	MAX912CSE+
MAX810TEUR+	MAX9032AKA+	MAX907ESA	MAX912EPE
MAX810TEXR+	MAX9032ASA+	MAX907ESA+	MAX912EPE+
MAX810ZEXR+T	MAX9032AUA+	MAX907MJA	MAX912ESE
MAX9000ESA+	MAX9034ASD+	MAX908CPD	MAX912ESE+
MAX9000EUA+	MAX9034AUD+	MAX908CPD+	MAX912MJE
MAX9002ESA+	MAX9038BABT+T	MAX908CSD	MAX913CPA
MAX9002EUA+	MAX9038BEBT+T	MAX908CSD+	MAX913CPA+
MAX9003ESA+	MAX903CPA+	MAX908EPD	MAX913CSA
MAX9003EUA+	MAX903CSA+	MAX908EPD+	MAX913CSA+
MAX9005ESA+	MAX903EPA+	MAX908ESD	MAX913EPA
MAX9005EUA+	MAX903ESA+	MAX908ESD+	MAX913EPA+
MAX9010EXT+	MAX9060EBS+G45	MAX908MJD	MAX913ESA
MAX9011EUT+	MAX9060EUK+	MAX9092AKA+T	MAX913ESA+
MAX9012ESA+	MAX9075EUK+	MAX9092AUA+	MAX913EUA+
MAX9012EUA+	MAX9075EXK+	MAX9094ASD+	MAX913MJA
MAX9013ESA+	MAX9077EKA+	MAX9094AUD+	MAX913MSA/PR

Multisim 14.1 Base Edition Components

MAX9140AAUK+	MAX921ESA+	MAX924CSE	MAX934CPE
MAX9140AAXK+	MAX921MJA	MAX924CSE+	MAX934CPE+
MAX9140EUK+	MAX922CPA	MAX924EPE	MAX934CSE
MAX9140EXK+	MAX922CPA+	MAX924EPE+	MAX934CSE+
MAX9141EKA+	MAX922CSA	MAX924ESE	MAX934EPE
MAX9141ESA+	MAX922CSA+	MAX924ESE+	MAX934EPE+
MAX9142EKA+	MAX922CUA+	MAX924MJE	MAX934ESE
MAX9142ESA+	MAX922EPA	MAX932CPA	MAX934ESE+
MAX9144ESD+	MAX922EPA+	MAX932CPA+	MAX941CPA
MAX9144EUD+	MAX922ESA	MAX932CSA	MAX941CPA+
MAX9201ESE+	MAX922ESA+	MAX932CSA+	MAX941CSA
MAX9201EUE+	MAX922MJA	MAX932CUA+	MAX941CSA+
MAX9202ESD+	MAX923CPA	MAX932EPA	MAX941CUA
MAX9202EUD+	MAX923CPA+	MAX932EPA+	MAX941EPA
MAX9203EKA+	MAX923CSA	MAX932ESA	MAX941EPA+
MAX9203ESA+	MAX923CSA+	MAX932ESA+	MAX941ESA
MAX921CPA	MAX923CUA	MAX933CPA	MAX941ESA+
MAX921CPA+	MAX923CUA+	MAX933CPA+	MAX941EUA+
MAX921CSA	MAX923EPA	MAX933CSA	MAX941MJA
MAX921CSA+	MAX923EPA+	MAX933CSA+	MAX942AUA+
MAX921CUA	MAX923ESA	MAX933CUA+	MAX942CPA
MAX921CUA+	MAX923ESA+	MAX933EPA	MAX942CPA+
MAX921EPA	MAX923MJA	MAX933EPA+	MAX942CSA
MAX921EPA+	MAX924CPE	MAX933ESA	MAX942CSA+
MAX921ESA	MAX924CPE+	MAX933ESA+	MAX942CUA+

Multisim 14.1 Base Edition Components

MAX942EPA	MAX953EPA	MAX961ESA+	MAX963ESD+
MAX942EPA+	MAX953EPA+	MAX961EUA+	MAX9643TATA+T
MAX942ESA	MAX953ESA	MAX9620AXK+	MAX9643UATA+T
MAX942ESA+	MAX953ESA+	MAX9622AXK+	MAX9644EBS+G45
MAX942EUA+	MAX953EUA+	MAX9626ATC+	MAX9644EUK+
MAX942MJA	MAX953MJA	MAX9627ATC+	MAX9645EUK+
MAX944CPD	MAX954EPA	MAX9628ATC+	MAX9647AUK+T
MAX944CPD+	MAX954EPA+	MAX962ESA	MAX9647AXK+T
MAX944CSD	MAX954ESA	MAX9632ASA+	MAX9648AUK+
MAX944CSD+	MAX954ESA+	MAX9632ATA+	MAX9648AXK+
MAX944EPD	MAX954EUA+	MAX9632AUA+	MAX964ESA
MAX944EPD+	MAX954MJA	MAX9633ASA+	MAX9650ATA+
MAX944ESD	MAX9550EUA+	MAX9633ATA+	MAX9650AUA+
MAX944ESD+	MAX9550EZK+	MAX9634FERS+	MAX9650AZK+
MAX944MJD	MAX9551EUA+	MAX9634FEUK+	MAX9651ATA+
MAX951EPA+	MAX9552EUD+	MAX9634HERS+	MAX9651AUA+
MAX951ESA+	MAX9600EUP+	MAX9634HEUK+	MAX965ESA+
MAX951EUA+	MAX9601EUP+	MAX9634TERS+	MAX965EUA+
MAX951MJA	MAX9602EUG+	MAX9634TEUK+	MAX9691EPA+
MAX952EPA	MAX9613AXT+	MAX9634WERS+	MAX9691ESA+
MAX952EPA+	MAX9615AXA+	MAX9634WEUK+	MAX9691EUA+
MAX952ESA	MAX9617AXT+	MAX9636AXT+	MAX9692EPE+
MAX952ESA+	MAX9618AXA+	MAX9637AXA+	MAX9692ESE+
MAX952EUA+	MAX9619AXT+	MAX9638AVB+	MAX9692EUB+
MAX952MJA	MAX961ESA	MAX963ESA	MAX9693EEE+

Multisim 14.1 Base Edition Components

MAX9693EPE+	MAX989ESA+	MAX992ESA+	MAX996ESD+
MAX9693ESE+	MAX989EUA+	MAX992EUA+	MAX996EUD+
MAX975ESA+	MAX990EKA+	MAX9934FART+	MAX997ESA+
MAX975EUA+	MAX990ESA+	MAX9934FAUA+	MAX997EUA+
MAX976ESA+	MAX990EUA+	MAX9934TART+	MAX998ESA+
MAX976EUA+	MAX9910EXK+	MAX9934TAUA+	MAX998EUT+
MAX976MUA/PR2	MAX9911EWT+	MAX9938FEBS+T	MAX999AAUK+5
MAX977EEE+	MAX9911EXT+	MAX9938FELT+	MAX999EUK+
MAX977ESD+	MAX9912EKA+	MAX9938FEUK+	MAXIM-MAXQ-HDR
MAX978EEE+	MAX9913EUB+	MAX9938HEBS+T	MB6S-E3/80
MAX978ESE+	MAX9915EXT+	MAX9938HEUK+	MBD770DWT1G
MAX985EBT+T	MAX9916EKA+	MAX9938TEBS+T	MBR030
MAX985ESA+	MAX9917EUB+	MAX9938TEUK+	MBR040
MAX985EUK+	MAX9918ASA+	MAX9938WEBS+	MBR0520L
MAX985EXK+	MAX9919FASA+	MAX9938WEUK+	MBR0520LT1
MAX986ESA+	MAX9919NASA+	MAX993ESD+	MBR0520LT1G
MAX986EUK+	MAX991EKA+	MAX993EUD+	MBR0520LT3G
MAX986EXK+	MAX991ESA+	MAX9943ATT+T	MBR0530
MAX987ESA+	MAX991EUA+	MAX9943AUA+	MBR0530T1
MAX987EUK+	MAX9920ASA+	MAX9944ASA+	MBR0530T1G
MAX987EXK+	MAX9928FABT+	MAX9944ATA+T	MBR0530T3G
MAX988ESA+	MAX9928FAUA+	MAX994ESD+	MBR0540T1
MAX988EUK+	MAX9929FABT+	MAX994EUD+	MBR0540T1G
MAX988EXK+	MAX9929FAUA+	MAX995ESD+	MBR0540T3G
MAX989EKA+	MAX992EKA+	MAX995EUD+	MBR10100

Multisim 14.1 Base Edition Components

MBR10100G	MBR120LSFT3G	MBR16100CTG	MBR20H100CTG
MBR10100MFST1G	MBR120VLSFT1G	MBR1635	MBR20H150CTG
MBR10100MFST3G	MBR120VLSFT3G	MBR1635G	MBR20H200CT-E3/45
MBR1035	MBR1240MFST1G	MBR1645	MBR20L45CTG
MBR1035G	MBR1240MFST3G	MBR1645G	MBR20L60CTG
MBR1045	MBR130LSFT1G	MBR16H45-E3/45	MBR230LSFT1G
MBR1045G	MBR130T1	MBR1H100SFT3G	MBR2520
MBR1045MFST1G	MBR130T1G	MBR20035CT	MBR2530
MBR1045MFST3G	MBR130T3G	MBR20045CT	MBR2535CT
MBR1060	MBR140ESFT1G	MBR20100	MBR2535CTG
MBR1060G	MBR140ESFT3G	MBR20100CTG	MBR2535CTL
MBR1080G	MBR140SFT1G	MBR20100CTH	MBR2535CTLG
MBR1090G	MBR140SFT3G	MBR20200CTG	MBR2540
MBR10H100CTG	MBR150G	MBR2030CTLG	MBR2545CT
MBR10H100CTHE3/45	MBR150RLG	MBR2035CT	MBR2545CTG
MBR10H100-E3/45	MBR1520	MBR2045CT	MBR2H100SFT3G
MBR10L60CTG	MBR1530	MBR2045CTG	MBR30035CT
MBR1100G	MBR1535CT	MBR2045EMFST1G	MBR30045CT
MBR1100RLG	MBR1535CTG	MBR2045EMFST3G	MBR3020CT
MBR12035CT	MBR1540	MBR2045MFST1G	MBR3035CT
MBR12045CT	MBR1545CT	MBR2045MFST3G	MBR3035PT
MBR120ESFT1G	MBR1545CT-E3/45	MBR2060CTG	MBR3045CT
MBR120ESFT3G	MBR1545CTG	MBR2080CTG	MBR3045PT
MBR120LSFT1G	MBR160G	MBR2090CTG	MBR3045PTG
	MBR160RLG	MBR20H100CT/45	

Multisim 14.1 Base Edition Components

MBR3045STG	MBR3545	MBR5100MFST3G	MBR735
MBR3045WTG	MBR3545H	MBR540MFST1G	MBR735G
MBR30H100CTG	MBR360G	MBR540MFST3G	MBR745
MBR30H100MFST1G	MBR360RLG	MBR560MFST1G	MBR745-E3/45
MBR30H100MFST3G	MBR4015CTLG	MBR560MFST3G	MBR745G
MBR30H150CTG	MBR4015LWT	MBR5825	MBR7520
MBR30H30CTG	MBR4015LWTG	MBR5825H	MBR7530
MBR30H60CTG	MBR4020	MBR5831	MBR7535
MBR30L45CTG	MBR40250G	MBR5831H	MBR7540
MBR30L60CTG	MBR40250TG	MBR5H100MFST1G	MBR7545
MBR3100G	MBR4030	MBR6035	MBR760-E3/45
MBR3100RLG	MBR4040	MBR6035B	MBR7H45-E3/45
MBR320M	MBR4045PT-E3/45	MBR6035PF	MBR8035
MBR320P	MBR4045PTG	MBR6045	MBR8045
MBR330M	MBR4045WTG	MBR6045B	MBR8H100MFST1G
MBR330P	MBR4060PT-E3/45	MBR6045H	MBR8H100MFST3G
MBR340	MBR40H100WTG	MBR6045PF	MBRA120ET3G
MBR340G	MBR40L45CTG	MBR6045PTG	MBRA130LT3
MBR340M	MBR40L60CTG	MBR6045WTG	MBRA130LT3G
MBR340P	MBR41H100CTG	MBR60H100CTG	MBRA140T3
MBR340RLG	MBR440MFST1G	MBR60L45CTG	MBRA140T3G
MBR350RLG	MBR440MFST3G	MBR60L45WTG	MBRA160T3
MBR3520	MBR460MFST1G	MBR6535	MBRA160T3G
MBR3535	MBR460MFST3G	MBR6545	MBRA1H100T3G
	MBR5100MFST1G	MBR7030WTL	MBRA210ET3G

Multisim 14.1 Base Edition Components

MBRA210LT3G	MBRB2515LG	MBRD1035CTL	MBRD650CTG
MBRA2H100T3G	MBRB2515LT4G	MBRD1035CTLG	MBRD650CTT4G
MBRA320T3G	MBRB2535CTLG	MBRD1035CTLT4G	MBRD660CTG
MBRA340T3G	MBRB2535CTLT4G	MBRD1045T4G	MBRD660CTRLG
MBRAF1100T3G	MBRB2545CTG	MBRD320G	MBRD660CTT4G
MBRAF1540T3G	MBRB2545CTT4G	MBRD320RLG	MBRD835L
MBRAF2H100T3G	MBRB3030CT	MBRD320T4G	MBRD835LG
MBRAF3200T3G	MBRB3030CTG	MBRD330G	MBRD835LT4G
MBRAF440T3G	MBRB3030CTL	MBRD330RLG	MBRF10H150CTG
MBRB1045G	MBRB3030CTLG	MBRD330T4G	MBRF10L60CTG
MBRB1045T4G	MBRB3030CTT4G	MBRD340G	MBRF20100CTG
MBRB1545CTG	MBRB3045CT-1G	MBRD340RLG	MBRF20200CTG
MBRB1545CTT4	MBRB30H30CT-1G	MBRD340T4G	MBRF2045CTG
MBRB1545CTT4G	MBRB30H60CT-1G	MBRD350G	MBRF2060CTG
MBRB1645T4G	MBRB30H60CT- E3/81	MBRD350RLG	MBRF20H100CTG
MBRB20100CTG	MBRB30H60CTT4G	MBRD350T4G	MBRF20H150CTG
MBRB20100CTT4	MBRB4030	MBRD360G	MBRF20L45CTG
MBRB20100CTT4G	MBRB4030G	MBRD360RLG	MBRF20L60CTG
MBRB20200CTG	MBRB4030T4G	MBRD360T4	MBRF20L80CTG
MBRB20200CTT4	MBRB41H100CT-1G	MBRD360T4G	MBRF2545CTG
MBRB20200CTT4G	MBRB41H100CTT4 G	MBRD5H100T4G	MBRF30H100CTG
MBRB2060CTG	MBRB60H100CTT4 G	MBRD620CTT4G	MBRF30H150CTG
MBRB2060CTT4G		MBRD630CTT4G	MBRF30H60CTG
MBRB20H100CTT4 G	MBRB8H100T4G	MBRD640CTT4	MBRF30L45CTG
		MBRD640CTT4G	MBRF30L60CTG

Multisim 14.1 Base Edition Components

MBRF40250TG	MBRS120T3G	MBRS360BT3G	MC1439G
MBRL030	MBRS130LT3	MBRS360T3	MC1439P1
MBRL040	MBRS130LT3G	MBRS360T3G	MC1456CG
MBRM110ET1G	MBRS130T3G	MBRS410ET3G	MC1456CP1
MBRM110ET3G	MBRS140T3	MBRS410LT3	MC1456G
MBRM110LT1G	MBRS140T3G	MBRS410LT3G	MC1456P1
MBRM110LT3G	MBRS1540T3G	MBRS4201T3G	MC1458CD
MBRM120ET1G	MBRS190T3	MBRS540T3	MC1458CG
MBRM120ET3G	MBRS190T3G	MBRS540T3G	MC1458CP1
MBRM120LT1	MBRS2040LT3	MBT2222ADW1T1G	MC1458CU
MBRM120LT1G	MBRS2040LT3G	MBT35200MT1	MC1458D
MBRM120LT3	MBRS230LT3G	MBT35200MT1G	MC1458G
MBRM120LT3G	MBRS240LT3	MBT3904DW1T1G	MC1458P
MBRM130LT1G	MBRS240LT3G	MBT3946DW1T1G	MC1458P1
MBRM130LT3	MBRS260T3G	MBT3946DW1T2G	MC1458SD
MBRM130LT3G	MBRS2H100T3G	MC1436CD	MC1458SG
MBRM140T1	MBRS3100T3G	MC1436CG	MC1458SP1
MBRM140T1G	MBRS3200T3	MC1436CP1	MC1458SU
MBRM140T3	MBRS3200T3G	MC1436CU	MC1458U
MBRM140T3G	MBRS3201T3G	MC1436D	MC1536G
MBRM1H100T3G	MBRS320T3	MC1436G	MC1536U
MBRM2H100T3G	MBRS320T3G	MC1436P1	MC1537L
MBRS1100T3	MBRS330T3G	MC1436U	MC1539G
MBRS1100T3G	MBRS340T3	MC1437L	MC1556G
MBRS120T3	MBRS340T3G	MC1437P	MC1556U

Multisim 14.1 Base Edition Components

MC1558FK	MC1747G	MC33071D	MC33074DTBR2G
MC1558G	MC1747L	MC33071DG	MC33074L
MC1558JG	MC1748CG	MC33071DR2G	MC33074P
MC1558SG	MC1748CP1	MC33071P	MC33074PG
MC1558SU	MC1748CU	MC33071PG	MC33077D
MC1558U	MC1748G	MC33071U	MC33077DG
MC1709AG	MC1748U	MC33072ADG	MC33077DR2G
MC1709AU	MC1776CD	MC33072ADR2G	MC33077P
MC1709CG	MC1776CG	MC33072AP	MC33077PG
MC1709CP1	MC1776CP1	MC33072APG	MC33078D
MC1709CU	MC1776CU	MC33072D	MC33078DG
MC1709G	MC1776G	MC33072DG	MC33078DR2G
MC1741CD	MC1776U	MC33072DR2G	MC33078P
MC1741CG	MC3301P	MC33072P	MC33078PG
MC1741CP1	MC3302DG	MC33072PG	MC33079D
MC1741CU	MC3302DR2G	MC33072U	MC33079DG
MC1741G	MC3302DTBR2G	MC33074ADG	MC33079DR2G
MC1741SCD	MC3302PG	MC33074ADR2G	MC33079P
MC1741SCG	MC3303D	MC33074ADTBG	MC33079PG
MC1741SCP1	MC3303L	MC33074ADTBR2G	MC33161DG
MC1741U	MC3303P	MC33074APG	MC33161DMR2G
MC1747CD	MC33071ADG	MC33074D	MC33161DR2G
MC1747CG	MC33071ADR2G	MC33074DG	MC33161PG
MC1747CL	MC33071AP	MC33074DR2G	MC33171D
MC1747CP2	MC33071APG	MC33074DTBG	MC33171DG

Multisim 14.1 Base Edition Components

MC33171DR2G	MC33272ADG	MC3403P	MC35001U
MC33171P	MC33272APG	MC3403PG	MC3503L
MC33171PG	MC33272D	MC3405L	MC3505L
MC33172D	MC33272P	MC3405P	MC35071AU
MC33172P	MC33274ADG	MC34071D	MC35071U
MC33174D	MC33274ADTBR2G	MC34071P	MC35080AU
MC33174P	MC33274APG	MC34071U	MC35080U
MC33178D	MC33274D	MC34080D	MC35171U
MC33178DG	MC33274P	MC34080P	MC35181U
MC33178DMR2G	MC33282D	MC34084DW	MC3558G
MC33178DR2G	MC33282P	MC34084P	MC3558U
MC33178P	MC33284D	MC34161DG	MC4558ACP1
MC33178PG	MC33284P	MC34161DMR2G	MC4558CD
MC33179D	MC3358P1	MC34161DR2G	MC4558CG
MC33179DG	MC34001D	MC34161PG	MC4558CP1
MC33179DR2G	MC34001G	MC34181D	MC4558CU
MC33179DTBR2G	MC34001P	MC34181P	MC4558G
MC33179P	MC34001U	MC3458D	MC4558U
MC33179PG	MC3401D	MC3458G	MC4741CD
MC33181D	MC3401P	MC3458P1	MC4741CL
MC33181P	MC3403D	MC3458U	MC4741CP
MC33182D	MC3403DG	MC3476G	MC4741L
MC33182P	MC3403DR2G	MC3476P1	MC68HC11D3CFBL
MC33184D	MC3403L	MC3476U	MC68HC11D3CFN1
MC33184P	MC3403N	MC35001G	MC68HC11D3CP1

Multisim 14.1 Base Edition Components

MC68HC11E0CFN2	MCP6001T-E/OT	MCP6021-I/ST	MCP603T-I/SN
MC68HC11E1CFN2	MCP6001T-I/LT	MCP6021T-E/OT	MCP603T-I/ST
MCH3209-TL-E	MCP6001T-I/OT	MCP6022-I/P	MCP6041-I/MS
MCH3377-TL-E	MCP6001UT-E/OT	MCP6022-I/SN	MCP6041-I/P
MCH3377-TL-H	MCP6001UT-I/OT	MCP6022-I/ST	MCP6041-I/SN
MCH3383-TL-H	MCP6002-E/MC	MCP6023-I/P	MCP6041T-I/OT
MCH3474-TL-E	MCP6002-E/P	MCP6023-I/SN	MCP6042-I/MS
MCH3474-TL-H	MCP6002-I/MS	MCP6023-I/ST	MCP6042-I/P
MCH3484-TL-H	MCP6002-I/P	MCP6024-I/P	MCP6042-I/SN
MCH6203-TL-E	MCP6002-I/SN	MCP6024-I/SL	MCP6043-I/MS
MCH6320-TL-E	MCP6002T-E/MS	MCP6024-I/ST	MCP6043-I/P
MCH6321-TL-E	MCP6002T-E/SN	MCP602T-I/P	MCP6043-I/SN
MCH6336-TL-E	MCP6004-E/P	MCP602T-I/SN	MCP6043T-I/CH
MCH6336-TL-H	MCP6004-I/P	MCP602T-I/ST	MCP6044-I/P
MCH6337-TL-E	MCP6004-I/SL	MCP6031-E/MS	MCP6044-I/SL
MCH6337-TL-H	MCP6004-I/ST	MCP6031-E/SN	MCP6044-I/ST
MCH6421-TL-E	MCP6004T-E/SL	MCP6031T-E/OT	MCP604T-I/P
MCH6436-TL-E	MCP6004T-E/ST	MCP6032-E/MS	MCP604T-I/SL
MCH6534-TL-E	MCP601-I/P	MCP6032-E/SN	MCP604T-I/ST
MCH6541-TL-E	MCP601-I/SN	MCP6033-E/MS	MCP6051T-E/MNY
MCH6604-TL-E	MCP601-I/ST	MCP6033-E/SN	MCP6051T-E/OT
MCH6613-TL-E	MCP601T-I/OT	MCP6034-E/SL	MCP6051T-E/SN
MCP6001RT-E/OT	MCP6021-E/MS	MCP6034-E/ST	MCP6052T-E/MNY
MCP6001RT-I/OT	MCP6021-I/P	MCP603T-I/CH	MCP6052T-E/SN
MCP6001T-E/LT	MCP6021-I/SN	MCP603T-I/P	MCP6054T-E/SL

Multisim 14.1 Base Edition Components

MCP6054T-E/ST	MCP609-I/P	MCP618-I/SN	MCP6241-E/MC
MCP6061T-E/MNY	MCP609-I/SL	MCP619-I/P	MCP6241-E/MS
MCP6061T-E/OT	MCP609-I/ST	MCP619-I/SL	MCP6241-E/P
MCP6061T-E/SN	MCP6141-I/MS	MCP619-I/ST	MCP6241-E/SN
MCP6062T-E/MNY	MCP6141-I/P	MCP621ST-E/OT	MCP6241RT-E/OT
MCP6062T-E/SN	MCP6141-I/SN	MCP621T-E/MNY	MCP6241T-E/OT
MCP6064T-E/SL	MCP6141T-E/OT	MCP621T-E/SN	MCP6241UT-E/LT
MCP6064T-E/ST	MCP6142-I/MS	MCP622T-E/MF	MCP6241UT-E/OT
MCP606-I/P	MCP6142-I/P	MCP622T-E/SN	MCP6242-E/MS
MCP606-I/SN	MCP6142-I/SN	MCP6231-E/MC	MCP6242-E/P
MCP606-I/ST	MCP6143-I/MS	MCP6231-E/MS	MCP6242-E/SN
MCP606T-I/OT	MCP6143-I/P	MCP6231-E/P	MCP6244-E/P
MCP6071T-E/MNY	MCP6143-I/SN	MCP6231-E/SN	MCP6244-E/SL
MCP6071T-E/OT	MCP6143T-E/CH	MCP6231RT-E/OT	MCP6244-E/ST
MCP6071T-E/SN	MCP6144-I/P	MCP6231T-E/OT	MCP624T-E/SL
MCP6072T-E/MNY	MCP6144-I/SL	MCP6231UT-E/LT	MCP624T-E/ST
MCP6072T-E/SN	MCP6144-I/ST	MCP6231UT-E/OT	MCP625T-E/MF
MCP6074T-E/SL	MCP616-I/MS	MCP6232-E/MS	MCP625T-E/UN
MCP6074T-E/ST	MCP616-I/P	MCP6232-E/P	MCP6271-E/MS
MCP607-I/P	MCP616-I/SN	MCP6232-E/SN	MCP6271-E/P
MCP607-I/SN	MCP617-I/MS	MCP6232T-E/MNY	MCP6271-E/SN
MCP607-I/ST	MCP617-I/P	MCP6234-E/P	MCP6271RT-E/OT
MCP608-I/P	MCP617-I/SN	MCP6234-E/SL	MCP6271T-E/OT
MCP608-I/SN	MCP618-I/MS	MCP6234-E/ST	MCP6272-E/MS
MCP608-I/ST	MCP618-I/P	MCP623T-E/CHY	MCP6272-E/P

Multisim 14.1 Base Edition Components

MCP6272-E/SN	MCP6284-E/SL	MCP631T-E/MNY	MCP6441T-E/LT
MCP6273-E/MS	MCP6284-E/ST	MCP631T-E/OT	MCP6441T-E/OT
MCP6273-E/P	MCP6285-E/MS	MCP631T-E/SN	MCP6442T-E/MNY
MCP6273-E/SN	MCP6285-E/P	MCP632T-E/MF	MCP6442T-E/MS
MCP6273T-E/CH	MCP6285-E/SN	MCP632T-E/SN	MCP6442T-E/SN
MCP6273T-E/SN	MCP6286T-E/OT	MCP633T-E/CHY	MCP6444T-E/SL
MCP6274-E/P	MCP6291-E/MS	MCP633T-E/SN	MCP6444T-E/ST
MCP6274-E/SL	MCP6291-E/P	MCP635T-E/MF	MCP6471T-E/LTY
MCP6274-E/ST	MCP6291-E/SN	MCP635T-E/UN	MCP6471T-E/OT
MCP6275-E/MS	MCP6291RT-E/OT	MCP6401RT-E/OT	MCP6472-E/MS
MCP6275-E/P	MCP6291T-E/OT	MCP6401T-E/LT	MCP6472-E/SN
MCP6275-E/SN	MCP6292-E/MS	MCP6401T-E/OT	MCP6472T-E/MNY
MCP6281-E/MS	MCP6292-E/P	MCP6401T-H/OT	MCP6472T-E/MS
MCP6281-E/P	MCP6292-E/SN	MCP6401UT-E/OT	MCP6472T-E/SN
MCP6281-E/SN	MCP6293-E/MS	MCP6402T-E/MNY	MCP6474-E/SL
MCP6281RT-E/OT	MCP6293-E/P	MCP6402T-E/SN	MCP6474-E/ST
MCP6281T-E/OT	MCP6293-E/SN	MCP6402T-H/SN	MCP6474T-E/SL
MCP6282-E/MS	MCP6293T-E/CH	MCP6404T-E/SL	MCP6474T-E/ST
MCP6282-E/P	MCP6294-E/P	MCP6404T-E/ST	MCP6481T-E/LTY
MCP6282-E/SN	MCP6294-E/SL	MCP6404T-H/SL	MCP6481T-E/OT
MCP6283-E/MS	MCP6294-E/ST	MCP6406T-H/OT	MCP6482-E/MS
MCP6283-E/P	MCP6295-E/MS	MCP6407T-H/SN	MCP6482-E/SN
MCP6283-E/SN	MCP6295-E/P	MCP6409T-H/SL	MCP6482T-E/MNY
MCP6283T-E/CH	MCP6295-E/SN	MCP6421T-E/LTY	MCP6482T-E/MS
MCP6284-E/P	MCP629T-E/ML	MCP6421T-E/OT	MCP6482T-E/SN

Multisim 14.1 Base Edition Components

MCP6484-E/SL	MCP6541RT-E/OT	MCP6544T-I/ST	MCP6548-I/MS
MCP6484-E/ST	MCP6541T-E/MS	MCP6546-E/P	MCP6548-I/P
MCP6484T-E/SL	MCP6541T-E/OT	MCP6546-I/MS	MCP6548-I/SN
MCP6484T-E/ST	MCP6541T-E/SN	MCP6546-I/P	MCP6548T-E/MS
MCP6491T-E/LTY	MCP6541T-I/LT	MCP6546-I/SN	MCP6548T-E/SN
MCP6491T-E/OT	MCP6541T-I/OT	MCP6546RT-E/OT	MCP6548T-I/MS
MCP6492-E/MS	MCP6541UT-E/OT	MCP6546RT-I/OT	MCP6548T-I/SN
MCP6492-E/SN	MCP6541UT-I/LT	MCP6546T-E/MS	MCP6549-E/P
MCP6492T-E/MNY	MCP6542-E/P	MCP6546T-E/OT	MCP6549-I/P
MCP6492T-E/MS	MCP6542-I/MS	MCP6546T-E/SN	MCP6549-I/SL
MCP6492T-E/SN	MCP6542-I/P	MCP6546T-I/LT	MCP6549-I/ST
MCP6494-E/SL	MCP6542-I/SN	MCP6546T-I/MS	MCP6549T-E/SL
MCP6494-E/ST	MCP6542T-E/MS	MCP6546T-I/OT	MCP6549T-E/ST
MCP6494T-E/SL	MCP6542T-E/SN	MCP6546T-I/SN	MCP6549T-I/SL
MCP6494T-E/ST	MCP6543-E/P	MCP6546UT-E/OT	MCP6549T-I/ST
MCP651ST-E/OT	MCP6543-I/P	MCP6546UT-I/LT	MCP654T-E/SL
MCP651T-E/MNY	MCP6543-I/SN	MCP6547-E/P	MCP654T-E/ST
MCP651T-E/SN	MCP6543T-E/MS	MCP6547-I/MS	MCP655T-E/MF
MCP652T-E/MF	MCP6543T-E/SN	MCP6547-I/P	MCP655T-E/UN
MCP652T-E/SN	MCP6543T-I/MS	MCP6547-I/SN	MCP6561RT-E/OT
MCP653T-E/CHY	MCP6544-E/P	MCP6547T-E/MS	MCP6561T-E/LT
MCP6541-E/P	MCP6544T-E/SL	MCP6547T-E/SN	MCP6561T-E/OT
MCP6541-I/MS	MCP6544T-E/ST	MCP6547T-I/MS	MCP6561UT-E/OT
MCP6541-I/P	MCP6544T-I/P	MCP6547T-I/SN	MCP6562T-E/MS
MCP6541-I/SN	MCP6544T-I/SL	MCP6548-E/P	MCP6562T-E/SN

Multisim 14.1 Base Edition Components

MCP6564T-E/SL	MCP662T-E/SN	MCP6H81T-E/MNY	MCP6L1T-E/OT
MCP6564T-E/ST	MCP663T-E/CHY	MCP6H81T-E/SN	MCP6L1T-E/SN
MCP6566RT-E/OT	MCP663T-E/SN	MCP6H82-E/SN	MCP6L2T-E/MS
MCP6566T-E/LT	MCP664T-E/SL	MCP6H82T-E/MNY	MCP6L2T-E/SN
MCP6566T-E/OT	MCP664T-E/ST	MCP6H82T-E/SN	MCP6L4T-E/SL
MCP6566UT-E/OT	MCP665T-E/MF	MCP6H84-E/SL	MCP6L4T-E/ST
MCP6567T-E/MS	MCP665T-E/UN	MCP6H84-E/ST	MCP6L71RT-E/OT
MCP6567T-E/SN	MCP669T-E/ML	MCP6H84T-E/SL	MCP6L71T-E/MS
MCP6569T-E/SL	MCP6H01T-E/MNY	MCP6H84T-E/ST	MCP6L71T-E/OT
MCP6569T-E/ST	MCP6H01T-E/SN	MCP6H91T-E/MNY	MCP6L71T-E/SN
MCP659T-E/ML	MCP6H02T-E/MNY	MCP6H91T-E/SN	MCP6L72T-E/MS
MCP65R41T- 1202E/CHY	MCP6H02T-E/SN	MCP6H92T-E/MNY	MCP6L72T-E/SN
	MCP6H04T-E/SL	MCP6H92T-E/SN	MCP6L74T-E/SL
MCP65R41T- 2402E/CHY	MCP6H04T-E/ST	MCP6H94T-E/SL	MCP6L74T-E/ST
	MCP6H71-E/SN	MCP6H94T-E/ST	MCP6L91RT-E/OT
MCP65R46T- 1202E/CHY	MCP6H71T-E/MNY	MCP6L01RT-E/OT	MCP6L91T-E/MS
	MCP6H71T-E/SN	MCP6L01T-E/LT	MCP6L91T-E/OT
MCP65R46T- 2402E/CHY	MCP6H72-E/SN	MCP6L01T-E/OT	MCP6L91T-E/SN
	MCP6H72T-E/MNY	MCP6L01UT-E/OT	MCP6L92T-E/MS
MCP660T-E/ML	MCP6H72T-E/SN	MCP6L02T-E/MS	MCP6L92T-E/SN
MCP660T-E/SL	MCP6H74-E/SL	MCP6L02T-E/SN	MCP6L94T-E/SL
MCP660T-E/ST	MCP6H74-E/ST	MCP6L04T-E/SL	MCP6L94T-E/ST
MCP661T-E/OT	MCP6H74T-E/SL	MCP6L04T-E/ST	MCP6N11-001E/SN
MCP661T-E/SN	MCP6H74T-E/ST	MCP6L1RT-E/OT	
MCP662T-E/MF	MCP6H81-E/SN	MCP6L1T-E/MS	
MCP662T-E/MS			MCP6N11-002E/SN
			MCP6N11-005E/SN

Multisim 14.1 Base Edition Components

MCP6N11-010E/SN	MCP6V07-E/SN	MCP6V31UT-E/OT	MCP6V82-E/MS
MCP6N11-100E/SN	MCP6V08-E/SN	MCP6V32-E/MS	MCP6V82T-E/MNY
MCP6N11T-001E/MNY	MCP6V08T-E/MNY	MCP6V32T-E/MNY	MCP6V82T-E/MS
MCP6N11T-002E/MNY	MCP6V11T-E/OT	MCP6V32T-E/MS	MCP6V84-E/ST
MCP6N11T-005E/MNY	MCP6V11UT-E/LT	MCP6V34-E/ST	MCP6V84T-E/ST
MCP6N11T-010E/MNY	MCP6V11UT-E/OT	MCP6V34T-E/ST	MCP6V91T-E/OT
MCP6N11T-100E/MNY	MCP6V12-E/MS	MCP6V61T-E/OT	MCP6V91UT-E/LTY
	MCP6V12T-E/MNY	MCP6V61UT-E/LTY	MCP6V91UT-E/OT
	MCP6V12T-E/MS	MCP6V61UT-E/OT	MCP6V92-E/MS
	MCP6V14-E/ST	MCP6V62-E/MS	MCP6V92T-E/MNY
MCP6N16-001E/MF	MCP6V14T-E/ST	MCP6V62T-E/MNY	MCP6V92T-E/MS
MCP6N16-001E/MS	MCP6V26T-E/MNY	MCP6V62T-E/MS	MCP6V94-E/ST
MCP6N16-010E/MF	MCP6V26T-E/MS	MCP6V64-E/ST	MCP6V94T-E/ST
MCP6N16-010E/MS	MCP6V26T-E/SN	MCP6V64T-E/ST	MCR08BT1G
MCP6N16-100E/MF	MCP6V27-E/MD	MCP6V71T-E/OT	MCR08MT1G
MCP6N16-100E/MS	MCP6V27-E/MS	MCP6V71UT-E/LTY	MCR100-3G
MCP6V01T-E/MNY	MCP6V27-E/SN	MCP6V71UT-E/OT	MCR100-3RLG
MCP6V01T-E/SN	MCP6V27T-E/MD	MCP6V72-E/MS	MCR1906_2
MCP6V02-E/MD	MCP6V27T-E/MS	MCP6V72T-E/MNY	MCR1906_3
MCP6V02-E/SN	MCP6V27T-E/SN	MCP6V72T-E/MS	MCR1906_4
MCP6V03-E/MNY	MCP6V28T-E/MNY	MCP6V74-E/ST	MCR1906_6
MCP6V03-E/SN	MCP6V28T-E/MS	MCP6V74T-E/ST	MCR1906_8
MCP6V06-E/SN	MCP6V28T-E/SN	MCP6V81T-E/OT	MCR22_2
MCP6V06T-E/MNY	MCP6V31T-E/OT	MCP6V81UT-E/LTY	MCR22_3
MCP6V07-E/MD	MCP6V31UT-E/LT	MCP6V81UT-E/OT	MCR22_4

Multisim 14.1 Base Edition Components

MCR22_6	MCR3935_10	MDA3550	MDA990-4
MCR22_8	MCR3935_2	MDA3551	MDA990-5
MCR220_5	MCR3935_3	MDA920A1	MDA990-6
MCR220_7	MCR3935_4	MDA920A2	MGP11N60ED
MCR220_9	MCR3935_5	MDA920A3	MGSF1N02LT1G
MCR221_5	MCR3935_6	MDA920A4	MGSF1N03LT1G
MCR221_7	MCR3935_7	MDA920A5	MGSF2N02ELT1G
MCR221_9	MCR3935_8	MDA920A6	MGW21N60ED
MCR3818_10	MCR3935_9	MDA920A7	MHD20N06C
MCR3818_2	MCR703AT4G	MDA920A8	MHD20N06G
MCR3818_3	MCR706AT4G	MDA920A9	MHD20N06P
MCR3818_4	MCR716T4G	MDA970A1	MICRO_4BIT_ALU
MCR3818_6	MCR8SNG	MDA970A2	MINI-DIN3
MCR3818_8	MDA2500	MDA970A3	MINI-DIN3S
MCR3835_1	MDA2501	MDA970A5	MINI-DIN4
MCR3835_10	MDA2502	MDA970A6	MINI-DIN4S
MCR3835_2	MDA2504	MDA980-1	MINI-DIN5
MCR3835_3	MDA2506	MDA980-2	MINI-DIN5S
MCR3835_4	MDA3500	MDA980-3	MINI-DIN6
MCR3835_5	MDA3501	MDA980-4	MINI-DIN6S
MCR3835_6	MDA3502	MDA980-5	MIPS-EJTAG-HDR
MCR3835_7	MDA3504	MDA980-6	MJ11012G
MCR3835_8	MDA3506	MDA990-1	MJ11015G
MCR3835_9	MDA3508	MDA990-2	MJ11016G
MCR3935_1	MDA3510	MDA990-3	MJ11028G

Multisim 14.1 Base Edition Components

MJ11032G	MJB45H11G	MJD243G	MJD41CRLG
MJ11033G	MJB45H11T4	MJD243T4G	MJD41CT4G
MJ14002G	MJB45H11T4G	MJD253-1G	MJD42C1G
MJ15001G	MJD112-1G	MJD253T4G	MJD42CG
MJ15003G	MJD112G	MJD2955-1G	MJD42CRLG
MJ15004G	MJD112RLG	MJD2955G	MJD42CT4G
MJ15015G	MJD112T4G	MJD2955T4G	MJD44E3T4G
MJ15016G	MJD117-1G	MJD3055G	MJD44H11-1G
MJ15022G	MJD117G	MJD3055T4G	MJD44H11G
MJ15023G	MJD117RLG	MJD31C1G	MJD44H11RLG
MJ15024G	MJD117T4G	MJD31CG	MJD44H11T4G
MJ15025G	MJD122G	MJD31CRLG	MJD44H11T5G
MJ21193G	MJD122T4G	MJD31CT4G	MJD45H11-1G
MJ21194G	MJD127G	MJD31T4G	MJD45H11G
MJ21195G	MJD127T4	MJD32CG	MJD45H11RLG
MJ21196G	MJD127T4G	MJD32CRLG	MJD45H11T4G
MJ2955G	MJD148T4	MJD32CT4	MJD47G
MJ4502G	MJD148T4G	MJD32CT4G	MJD47T4G
MJ802G	MJD200G	MJD32RLG	MJD50G
MJB41CG	MJD200RLG	MJD32T4G	MJD50T4G
MJB41CT4G	MJD200T4G	MJD340G	MJD5731T4G
MJB42CT4G	MJD210G	MJD340RLG	MJD6039T4G
MJB44H11G	MJD210RLG	MJD340T4G	MJE13003G
MJB44H11T4	MJD210T4	MJD350G	MJE13005G
MJB44H11T4G	MJD210T4G	MJD350T4G	MJE13007G

Multisim 14.1 Base Edition Components

MJE13009G	MJE2955TG	MJF15031G	MKP3V120RLG
MJE15028G	MJE3055TG	MJF18004G	MKP3V240G
MJE15029G	MJE340G	MJF18008G	MKP3V240RLG
MJE15030G	MJE3439G	MJF2955G	MM3Z10VT1G
MJE15031G	MJE344G	MJF3055G	MM3Z12VST1G
MJE15032G	MJE350G	MJF31CG	MM3Z12VT1G
MJE15033G	MJE371G	MJF32CG	MM3Z15VST1G
MJE15034G	MJE4343G	MJF44H11G	MM3Z15VT1G
MJE15035G	MJE4353G	MJF45H11G	MM3Z18VT1G
MJE170G	MJE5730G	MJH11021G	MM3Z20VT1G
MJE171G	MJE5731AG	MJH11022G	MM3Z2V4T1G
MJE172G	MJE5731G	MJH6284G	MM3Z2V7T1G
MJE18002G	MJE5742G	MJH6287G	MM3Z30VT1G
MJE18004G	MJE5850G	MJL1302AG	MM3Z36VT1G
MJE18006G	MJE5851G	MJL21193G	MM3Z39VT1G
MJE18008G	MJE5852G	MJL21194G	MM3Z3V0T1G
MJE180G	MJE700G	MJL21195G	MM3Z3V3ST1G
MJE181G	MJE702G	MJL21196G	MM3Z3V6T1G
MJE182G	MJE703G	MJL3281AG	MM3Z3V9T1G
MJE200G	MJE800G	MJL4281AG	MM3Z43VT1G
MJE210G	MJE802G	MJL4302AG	MM3Z4V3ST1G
MJE243G	MJE803G	MJW18020G	MM3Z4V7T1G
MJE253G	MJF122G	MJW21196G	MM3Z5V1T1G
MJE270G	MJF127G	MJW3281AG	MM3Z5V6ST1G
MJE271G	MJF15030G	MKP3V120G	MM3Z6V8ST1G

Multisim 14.1 Base Edition Components

MM3Z8V2ST1G	MM5Z5V6T1G	MMBD717LT1G	MMBT3904
MM5Z10VT1G	MM5Z6V2ST1G	MMBD770T1G	MMBT3904LT1
MM5Z12VT1G	MM5Z6V2T1G	MMBD914LT1	MMBT3904LT1G
MM5Z15VT1G	MM5Z6V8ST1G	MMBD914LT1G	MMBT3904LT3G
MM5Z16VT1G	MM5Z6V8T1G	MMBD914LT3G	MMBT3904TT1G
MM5Z18VT1G	MM5Z7V5T1G	MMBF0201NLT1G	MMBT3906
MM5Z20VT1G	MM5Z8V2ST1G	MMBF170LT1G	MMBT3906TT1G
MM5Z24VT1G	MM5Z8V2T1G	MMBF4393LT1G	MMBT4401LT1
MM5Z27VT1G	MM5Z9V1ST1G	MMBF4393LT3G	MMBT4401LT1G
MM5Z2V4ST1G	MM5Z9V1T1G	MMBFJ175LT1G	MMBT4401LT3G
MM5Z2V4T1G	MMBD101LT1G	MMBFJ177LT1G	MMBT4401M3T5G
MM5Z2V7T1G	MMBD2835LT1G	MMBFJ309LT1G	MMBT4403LT1
MM5Z33VT1G	MMBD2836LT1G	MMBT2222A	MMBT4403LT1G
MM5Z36VT1G	MMBD2837LT1G	MMBT2222ALT1	MMBT4403LT3G
MM5Z3V0T1G	MMBD2838LT1G	MMBT2222ALT1G	MMBT4403M3T5G
MM5Z3V3T1G	MMBD301LT1	MMBT2222ALT3G	MMBT489LT1G
MM5Z3V6T1G	MMBD301LT1G	MMBT2369ALT1G	MMBT5401LT1
MM5Z47VT1G	MMBD301LT3G	MMBT2484LT1G	MMBT5401LT1G
MM5Z4V3T1G	MMBD301M3T5G	MMBT2484LT3G	MMBT5401LT3G
MM5Z4V7ST1G	MMBD352LT1G	MMBT2907ALT1	MMBT5551LT1
MM5Z4V7ST5G	MMBD353LT1G	MMBT2907ALT1G	MMBT5551LT1G
MM5Z4V7T1G	MMBD4148	MMBT2907ALT3G	MMBT5551LT3G
MM5Z5V1ST1G	MMBD7000LT1	MMBT2907AM3T5 G	MMBT5551M3T5G
MM5Z5V1T1G	MMBD7000LT1G	MMBT2907AWT1G	MMBT589LT1
MM5Z5V6ST1G	MMBD7000LT3G		MMBT589LT1G

Multisim 14.1 Base Edition Components

MMBT6428LT1G	MMBTH10LT3G	MMBZ33VALT1G	MMDL914T3G
MMBT6429LT1G	MMBV105GLT1G	MMBZ33VCL	MMFT960T1G
MMBT6517LT1	MMBV3401LT1G	MMBZ5221BLT1G	MMG05N60D
MMBT6517LT1G	MMBV3401LT3	MMBZ5222BLT1G	MMJT350T1G
MMBT6517LT3G	MMBV3401LT3G	MMBZ5226BLT1G	MMQA15VT1G
MMBT6520LT1	MMBZ10VAL	MMBZ5231BLT1G	MMQA20VT1G
MMBT6520LT1G	MMBZ12VAL	MMBZ5231BLT3G	MMQA20VT3G
MMBTA06LT1	MMBZ12VDL	MMBZ5232BLT1G	MMQA5V6T1G
MMBTA06LT1G	MMBZ15VAL	MMBZ5240BLT1G	MMQA5V6T3G
MMBTA06LT3G	MMBZ15VALT1	MMBZ5242BLT1G	MMQA6V2T1G
MMBTA06WT1G	MMBZ15VALT1G	MMBZ5242BLT3G	MMSD301T1
MMBTA14LT1G	MMBZ15VDL	MMBZ5248BLT1G	MMSD301T1G
MMBTA42	MMBZ15VDLT1G	MMBZ5248BLT3G	MMSD4148T1
MMBTA42LT1	MMBZ15VDLT3G	MMBZ5254BLT1G	MMSD4148T1G
MMBTA42LT1G	MMBZ18VAL	MMBZ5256BLT1G	MMSD4148T3G
MMBTA42LT3G	MMBZ18VCL	MMBZ5270BLT1G	MMSF3P02HD
MMBTA56LT1	MMBZ20VAL	MMBZ5V6AL	MMSZ10T1G
MMBTA56LT1G	MMBZ20VALT1G	MMBZ5V6ALT1G	MMSZ12T1G
MMBTA56LT3G	MMBZ20VCL	MMBZ5V6ALT3G	MMSZ2V7T1G
MMBTA63LT1G	MMBZ27VAL	MMBZ6V2AL	MMSZ2V7T3G
MMBTA92	MMBZ27VALT1G	MMBZ6V8AL	MMSZ3V3T1G
MMBTA92LT1G	MMBZ27VALT3G	MMBZ9V1AL	MMSZ4678T1G
MMBTA92LT3G	MMBZ27VCL	MMDL770T1G	MMSZ4679T1G
MMBTH10-4LT1G	MMBZ27VCLT1G	MMDL914T1	MMSZ4681T1G
MMBTH10LT1G	MMBZ33VAL	MMDL914T1G	MMSZ4683T1G

Multisim 14.1 Base Edition Components

MMSZ4688T1G	MMSZ5240BT1G	MMUN2111LT1G	MMVL3401T1G
MMSZ4689T1G	MMSZ5242BT1G	MMUN2111LT3G	MONOSTABLE_VIRTUAL
MMSZ4689T3G	MMSZ5242BT3G	MMUN2112LT1G	MOS_N
MMSZ4690T1G	MMSZ5243BT1G	MMUN2113LT1G	MOS_N_4T
MMSZ4690T3G	MMSZ5245BT1G	MMUN2113LT3G	MOS_N_4T_DEP
MMSZ4691T1G	MMSZ5246BT1G	MMUN2114LT1G	MOS_N_DEP
MMSZ4692T1G	MMSZ5254BT1G	MMUN2114LT3G	MOS_P
MMSZ4696T1G	MMSZ5258BT1G	MMUN2115LT1G	MOS_P_4T
MMSZ4699T1G	MMSZ5258BT3G	MMUN2116LT1G	MOS_P_4T_DEP
MMSZ4705T1G	MMSZ5259BT1G	MMUN2130LT1G	MOS_P_DEP
MMSZ4706T1G	MMSZ5260BT1G	MMUN2131LT1G	MOTOR_1A
MMSZ4707T1G	MMSZ5262BT1G	MMUN2132LT1G	MOTOR_1C
MMSZ4715T1G	MMSZ5263BT1G	MMUN2134LT1G	MOTOR_2A
MMSZ5221BT1G	MMT05B230T3G	MMUN2211LT1G	MOTOR_2C
MMSZ5222BT1G	MMT05B260T3G	MMUN2211LT3G	MOTOR_3A
MMSZ5225BT1G	MMT05B310T3G	MMUN2212LT1G	MOTOR_3C
MMSZ5226BT1G	MMT05B350T3G	MMUN2213LT1G	MOTOR_4A
MMSZ5228BT1G	MMT08B064T3G	MMUN2214LT1G	MOTOR_4C
MMSZ5231BT1G	MMT08B260T3G	MMUN2215LT1G	MOTOR_VIRTUAL
MMSZ5231BT3G	MMT08B310T3G	MMUN2216LT1G	MPC-BDM-HDR
MMSZ5234BT1G	MMT08B350T3G	MMUN2231LT1G	MPS2907AG
MMSZ5235BT1G	MMT10B230T3G	MMUN2232LT1G	MPS2907ARLG
MMSZ5235BT3G	MMT10B260T3G	MMUN2233LT1G	MPS2907ARLRAG
MMSZ5236BT1G	MMT10B310T3G	MMUN2234LT1G	MPS2924
MMSZ5239BT1G	MMT10B350T3G	MMUN2238LT1G	

Multisim 14.1 Base Edition Components

MPS2925	MPS6520	MPSA42	MPSW51A
MPS2926	MPS6521	MPSA42G	MPSW51AG
MPS3392	MPS6522	MPSA43	MPSW51ARLRAG
MPS3393	MPS6523	MPSA43G	MPSW51ARLRPG
MPS3395	MPS6531	MPSA55	MPSW51G
MPS3638A	MPS6533	MPSA56	MPSW55
MPS3644	MPS6534	MPSA56G	MPSW56
MPS3646	MPS6562	MPSA56RLRAG	MR1120
MPS3702	MPS6565	MPSA56RLRMG	MR1366
MPS3703	MPS6566	MPSA56RLRPG	MR1376
MPS3704	MPS6571	MPSA56ZL1G	MR1386
MPS3707	MPS8098	MPSA70	MR1396
MPS3711	MPS8099	MPSA92	MR2400
MPS3826	MPS8598	MPSA93	MR2400F
MPS3827	MPSA05	MPSH10	MR2401
MPS3904	MPSA06	MPSL01	MR2401F
MPS5172	MPSA06G	MPSL51	MR2402
MPS5179	MPSA06RL1G	MPSW01	MR2402F
MPS6512	MPSA06RLG	MPSW01A	MR2404
MPS6513	MPSA06RLRAG	MPSW06G	MR2404F
MPS6514	MPSA06RLRMG	MPSW06RLRAG	MR2406
MPS6515	MPSA06RLRPG	MPSW10	MR2406F
MPS6516	MPSA10	MPSW42	MR2500
MPS6517	MPSA18	MPSW45G	MR2501
MPS6518	MPSA20	MPSW51	MR2502

Multisim 14.1 Base Edition Components

MR2504	MR752	MR856	MRS1504T3G
MR2506	MR754	MR860	MSB92T1G
MR2508	MR756	MR861	MSD1328-RT1G
MR2510	MR810	MR862	MSD602-RT1G
MR327	MR811	MR864	MSE1PJHM3/89A
MR328	MR812	MR866	MSP3V3HM3/89A
MR330	MR813	MR870	MSP430P325IFN
MR331	MR814	MR871	MSP430P325IPG
MR500	MR816	MR872	MSP430P325IPM
MR5005	MR817	MR874	MSQA6V1W5T2G
MR501	MR818	MR876	MSR1560G
MR5010	MR820	MRA4003T3G	MSR860G
MR502	MR821	MRA4004T3G	MSRD620CTG
MR5020	MR822	MRA4005T1G	MSRD620CTRG
MR5030	MR824	MRA4005T3G	MSRD620CTT4
MR504	MR826	MRA4006T3G	MSRD620CTT4G
MR5040	MR830	MRA4007T3G	MSRD620CTT4RG
MR5059	MR831	MRF5711LT1	MSRF1560G
MR506	MR832	MRF5812	MSRF860G
MR5060	MR834	MRF9011LT1	MSS1P3LHM3/89A
MR5061	MR836	MRF9011LT1_A	MSS1P4HM3/89A
MR508	MR850	MRF9011LT1_B	MSS1P6HM3/89A
MR510	MR851	MRF9411LT1	MSS2P3HM3/89A
MR750	MR852	MRF947T1	MTB20N20E
MR751	MR854	MRF9511LT1	MTB50P03HDLT4G

Multisim 14.1 Base Edition Components

MTD10P06HDL	MTP15N06E	MUN2111T1G	MUN2240T1G
MTD15N06V	MTP20P06	MUN2112T1G	MUN5111DW1T1G
MTD1N60E	MTP25N06	MUN2113T1G	MUN5111T1G
MTD1N80E	MTP25N06L	MUN2114T1G	MUN5112DW1T1G
MTD2955E	MTP25N10E	MUN2115T1G	MUN5112T1G
MTD2N50E	MTP2N50	MUN2135T1G	MUN5113DW1T1G
MTD3055V	MTP2P50	MUN2138T1G	MUN5113T1G
MTD3055VL	MTP2P50EG	MUN2141T1G	MUN5113T3G
MTD4N20E	MTP3055E/MC	MUN2211T1	MUN5114DW1T1G
MTD4P06	MTP3055V	MUN2211T1G	MUN5114T1G
MTD5N06	MTP3055VL	MUN2211T3G	MUN5115DW1T1G
MTD6N15T4G	MTP30N08M	MUN2212T1G	MUN5115T1G
MTD6N20ET4G	MTP35N06E	MUN2213T1	MUN5116DW1T1G
MTH13N50	MTP3N100	MUN2213T1G	MUN5131T1G
MTH30N20	MTP40N06M	MUN2214T1G	MUN5132T1G
MTH5N100	MTP4N50	MUN2214T3G	MUN5133DW1T1G
MTH8N60	MTP4N85	MUN2215T1G	MUN5133T1G
MTM10N100E	MTP50N05EL	MUN2216T1G	MUN5135DW1T1G
MTM15N40	MTP50N06E	MUN2230T1G	MUN5135T1G
MTM24N50E	MTP6N60	MUN2232T1G	MUN5140T1G
MTM26N40E	MTP6N60/MC	MUN2233T1G	MUN5211DW1T1G
MTM8N60	MTP7N20	MUN2234T1G	MUN5211T1
MTP10N05E/MC	MTP8N50E	MUN2236T1G	MUN5211T1G
MTP12P10	MTP8P10	MUN2237T1G	MUN5212DW1T1G
MTP15N05E	MULTIPLIER	MUN2238T1G	MUN5212T1G

Multisim 14.1 Base Edition Components

MUN5213DW1T1G	MUN5316DW1T1G	MUR130G	MUR1620CT
MUN5213DW1T3G	MUN5330DW1T1G	MUR130RLG	MUR1620CTG
MUN5213T1G	MUN5333DW1T1G	MUR140G	MUR1620CTRG
MUN5214DW1T1G	MUN5334DW1T1G	MUR140RLG	MUR1640CTG
MUN5214T1G	MUN5335DW1T1G	MUR1505	MUR1660CTG
MUN5215DW1T1G	MUN5335DW1T2G	MUR1510	MUR180EG
MUN5215T1G	MUN5336DW1T1G	MUR1510G	MUR180ERLG
MUN5216DW1T1G	MUR10005CT	MUR1515	MUR2020RG
MUN5230DW1T1G	MUR10010CT	MUR1515G	MUR2100EG
MUN5230T1G	MUR10015CT	MUR1520	MUR2100ERLG
MUN5232DW1T1G	MUR10020CT	MUR1520G	MUR210G
MUN5232T1G	MUR10150E	MUR1530	MUR210RLG
MUN5233DW1T1G	MUR105	MUR1540	MUR220G
MUN5233T1G	MUR105G	MUR1540G	MUR220RLG
MUN5235DW1T1G	MUR105RLG	MUR1550	MUR240G
MUN5237DW1T1G	MUR110	MUR1560	MUR240RLG
MUN5238T1G	MUR1100EG	MUR1560G	MUR2505
MUN5240T1G	MUR1100ERLG	MUR160	MUR2510
MUN5241T1G	MUR110G	MUR1605CT	MUR2515
MUN5311DW1T1G	MUR110RLG	MUR160G	MUR2520
MUN5312DW1T1G	MUR115	MUR160RLG	MUR260G
MUN5312DW1T2G	MUR115G	MUR1610CT	MUR260RLG
MUN5313DW1T1G	MUR115RLG	MUR1610CTG	MUR3005PT
MUN5314DW1T1G	MUR120G	MUR1615CT	MUR3010PT
MUN5315DW1T1G	MUR120RLG	MUR1615CTG	MUR3015PT

Multisim 14.1 Base Edition Components

MUR3020PT	MUR5005	MUR860G	MURB1620CTT4G
MUR3020PTG	MUR5010	MUR880EG	MURB1660CTG
MUR3020WTG	MUR5015	MURA105T3G	MURB1660CTT4G
MUR3040PTG	MUR5020	MURA110T3	MURD320T4
MUR3060PTG	MUR550APFRLG	MURA110T3G	MURD320T4G
MUR3060WTG	MUR550PFG	MURA115T3G	MURD330T4G
MUR405	MUR605CT	MURA120T3	MURD340T4G
MUR405G	MUR610CT	MURA120T3G	MURD530T4G
MUR410	MUR615CT	MURA130T3G	MURD550PFT4G
MUR4100EG	MUR620CT	MURA140T3	MURD620CT
MUR4100ERLG	MUR620CTG	MURA140T3G	MURD620CTG
MUR410G	MUR805	MURA160T3	MURD620CTT4
MUR410RLG	MUR805G	MURA160T3G	MURD620CTT4G
MUR415	MUR810	MURA205T3G	MURF1560G
MUR415G	MUR8100EG	MURA210T3G	MURF1620CTG
MUR415RLG	MUR810G	MURA215T3	MURF1660CTG
MUR420	MUR815	MURA215T3G	MURF550PFG
MUR420G	MUR815G	MURA220T3	MURF860G
MUR420RLG	MUR820	MURA220T3G	MURH840CTG
MUR440G	MUR820G	MURA230T3G	MURH860CTG
MUR440RLG	MUR830	MURA240T3G	MURHB840CTG
MUR460G	MUR840	MURB1620CTG	MURHB840CTT4
MUR460RLG	MUR840G	MURB1620CTRG	MURHB840CTT4G
MUR480EG	MUR850	MURB1620CTRT4G	MURHB860CTT4G
MUR480ERLG	MUR860	MURB1620CTT4	MURHD560T4G

Multisim 14.1 Base Edition Components

MURHD560W1T4G	MURS340T3	MZ4102	MZ5528B
MURHF860CTG	MURS340T3G	MZ4103	MZ5529B
MURHS160T3G	MURS360BT3G	MZ4104	MZ5530B
MURS105T3G	MURS360-E3/57T	MZ4614	MZPY10
MURS110T3	MURS360T3	MZ4615	MZPY100
MURS110T3G	MURS360T3G	MZ4616	MZPY11
MURS115T3	MURS480ET3G	MZ4617	MZPY12
MURS115T3G	MUSHROOM_HEAD	MZ4618	MZPY13
MURS120T3	MUX_16TO1	MZ4619	MZPY15
MURS120T3G	MUX_2TO1	MZ4620	MZPY16
MURS140T3	MUX_4TO1	MZ4621	MZPY18
MURS140T3G	MUX_8TO1	MZ4622	MZPY20
MURS160-E3/52T	MUX_LATCH	MZ4623	MZPY22
MURS160T3	MUX2_1	MZ4624	MZPY24
MURS160T3G	MUX2_1_INV	MZ4625	MZPY27
MURS205T3G	MUX2_1INV_3S	MZ4626	MZPY3.9
MURS210T3G	MUX4_1	MZ4627	MZPY30
MURS220T3	MUX4_1_INVO	MZ5520B	MZPY33
MURS220T3G	MUX8_1	MZ5521B	MZPY36
MURS230T3	MVGSF1N03LT1G	MZ5522B	MZPY39
MURS230T3G	MVMBF0201NLT1G	MZ5523B	MZPY4.3
MURS240T3G	myRIO_MXP	MZ5524B	MZPY4.7
MURS310T3	MZ4099	MZ5525B	MZPY43
MURS320T3	MZ4100	MZ5526B	MZPY47
MURS320T3G	MZ4101	MZ5527B	MZPY5.1

Multisim 14.1 Base Edition Components

MZPY5.6	NAND5	NCP1117DT33G	NCR401T
MZPY51	NAND6	NCP1117DT33RKG	NCR401U
MZPY56	NAND6	NCP1117DT33T5G	NCR402T
MZPY6.2	NAND7	NCP1117DT50G	NCR402U
MZPY6.8	NAND7	NCP1117DT50RKG	NCR405U
MZPY62	NAND8	NCP1117DTAG	NCS2001SN1T1G
MZPY68	NAND8	NCP1117DTARKG	NCS2001SN2T1G
MZPY7.5	NBRB8H100T4G	NCP1117DTAT5G	NCS2001SQ1T2G
MZPY75	NBRD5H100T4G	NCP1117ST12T3G	NCS2001SQ2T2G
MZPY8.2	NBR52H100T3G	NCP1117ST15T3G	NCS2200SN1T1G
MZPY82	NC_CONTACT	NCP1117ST18T3G	NCS2200SN2T1G
MZPY9.1	NCP1117DT12G	NCP1117ST20T3G	NCS2200SQ2T2G
MZPY91	NCP1117DT12RKG	NCP1117ST25T3G	NCS2200SQLT1G
N2550-6002RB	NCP1117DT15G	NCP1117ST285T3G	NCS2202SN1T1G
N80C196KB	NCP1117DT15RKG	NCP1117ST33T3G	NCS2202SN2T1G
N83C196KB	NCP1117DT18G	NCP1117ST50T3G	NCS2202SQ1T2G
N87C196KB	NCP1117DT18RKG	NCP1117STAT3G	NCS2202SQ2T2G
NAND13	NCP1117DT18T5G	NCP511SN15T1G	NCV1117DT15RKG
NAND2	NCP1117DT20G	NCP511SN18T1G	NCV1117DT18RKG
NAND2	NCP1117DT20RKG	NCP511SN25T1G	NCV1117DT18T5G
NAND3	NCP1117DT25G	NCP511SN27T1G	NCV1117DT20RKG
NAND3	NCP1117DT25RKG	NCP511SN28T1G	NCV1117DT25RKG
NAND4	NCP1117DT25T5G	NCP511SN30T1G	NCV1117DT33T5G
NAND4	NCP1117DT285G	NCP511SN33T1G	NCV1117DT50RKG
NAND5	NCP1117DT285RKG	NCP511SN50T1G	NCV1117DTARKG

Multisim 14.1 Base Edition Components

NCV1117ST12T3G	NCV4274CDT50RKG	NDF06N62ZG	NDS9953
NCV1117ST15T3G	NCV833DR2G	NDF08N50ZG	NDS9953A
NCV1117ST18T3G	NDD02N60Z-1G	NDF08N50ZH	NDS9955
NCV1117ST20T3G	NDD02N60ZT4G	NDF08N60ZG	NDS9956A
NCV1117ST25T3G	NDD03N50Z-1G	NDF08N60ZH	NDS9958
NCV1117ST33T3G	NDD03N50ZT4G	NDF10N60ZG	NDS9959
NCV1117ST50T3G	NDD03N60Z-1G	NDF10N60ZH	NE5532AI
NCV1117STAT3G	NDD03N60ZT4G	NDF10N62ZG	NE5532AIP
NCV2001SN2T1G	NDD04N50Z-1G	NDF11N50ZG	NE5532AP
NCV2001SQ2T2G	NDD04N50ZT4G	NDF11N50ZH	NE5532IP
NCV2901DR2G	NDD04N60Z-1G	NDF9406	NE5532P
NCV2901DTBR2G	NDD04N60ZT4G	NDF9407	NE5534AD
NCV2902DR2G	NDD05N50Z-1G	NDF9409	NE5534AP
NCV2902DTBR2G	NDD05N50ZT4G	NDF9410	NE5534D
NCV2903DMR2G	NDF02N60ZG	NDS8852H	NE5534P
NCV2903DR2G	NDF02N60ZH	NDS8858H	NET_10
NCV2904DMR2G	NDF03N60ZG	NDS8936	NET_12
NCV2904DR2G	NDF03N60ZH	NDS8947	NET_14
NCV33074ADTBR2 G	NDF04N60ZG	NDS9936	NET_16
	NDF04N60ZH	NDS9942	NET_18
NCV33074DR2G	NDF04N62ZG	NDS9943	NET_2
NCV33272ADR2G	NDF05N50ZG	NDS9947	NET_20
NCV4274CDS33R4G	NDF05N50ZH	NDS9948	NET_3
NCV4274CDS50R4G	NDF06N60ZG	NDS9952	NET_4
NCV4274CDT33RKG	NDF06N60ZH	NDS9952A	NET_6

Multisim 14.1 Base Edition Components

NET_8	NI_50MIL_68_RA	NI_sbRIO_P3_PORT S	NI-DAQPad-6020E
NF5101	NI_50MIL_68_V		NI-DAQPad-6052E
NF5102	NI_cRIO_4LED_RA	NI_sbRIO_P4_CON N	NI-ExpressCard- GPIO
NF5103	NI_cRIO_BNC	NI_sbRIO_P4_PORT S	NIF9N05CLT1G
NF5301	NI_cRIO_DSUB25M		NIF9N05CLT3G
NGB18N40CLBT4G	NI_cRIO_DSUB37M	NI_sbRIO_P5_CON N	NI-GPIB-ENET/100
NGB8207NT4G	NI_cRIO_INTERFAC E_GENERIC	NI_sbRIO_P5_PORT S	NI-GPIB-ENET/1000
NGD15N41CLT4G	NI_cRIO_INTERFAC E_ID	NI_VHDCI_68_RA	NI-GPIB-PCII/IIA
NGD18N40CLBT4G		NI_VHDCI_68_V	NI-GPIB-RS232
NGD8201NT4G	NI_cRIO_INTERFAC E_PARALLEL	NI-78xxR_RDIO	NI-GPIB-RS485/422
NGTB03N60R2DT4 G	NI_cRIO_INTERFAC E_SPI	NI-9683_AI	NI-GPIB-USB-HS
NGTB05N60R2DT4 G	NI_cRIO_INTERFAC E_USER	NI-9683_AIO	NI-myDAQ
NGTB10N60R2DT4 G	NI_cRIO_SCREWTE RM10	NI-9683_DI	NI-PCI-6011E
NGTB15N60R2FG		NI-9683_DO	NI-PCI-6013
NGTB20N60L2TF1G	NI_sbRIO_J5_CONN	NI- 9683_HALFBRIDGE_ DO	NI-PCI-6014
NGTB30N60L2WG	NI_sbRIO_J6_CONN		NI-PCI-6023E
NGTG20N60L2TF1G	NI_sbRIO_J7_CONN	NI-9683_LVTTL	NI-PCI-6024E
NHPJ08S600G	NI_sbRIO_J7_PORT S	NI-AT-GPIB/TNT	NI-PCI-6030E
NHPJ15S600G		NID9N05CLT4G	NI-PCI-6032E
NHPV08S600G	NI_sbRIO_P2_CON N	NI-DAQCard-6024E	NI-PCI-6034E
NHPV15S600G	NI_sbRIO_P2_PORT S	NI-DAQCard-6036E	NI-PCI-6035E
NI_2VHDCI_68_68_ RA	NI_sbRIO_P3_CON N	NI-DAQCard-6062E	NI-PCI-6036E
		NI-DAQPad- 6015(Mass.Term.)	NI-PCI-6040E
			NI-PCI-6052E

Multisim 14.1 Base Edition Components

NI-PCI-6070E	NI-PCI-6255	NI-PCle-7841R_RMIO	NI-PXI-6133
NI-PCI-6110	NI-PCI-6259		NI-PXI-6143
NI-PCI-6111	NI-PCI-6280	NI-PCle-7842R_RMIO	NI-PXI-6221
NI-PCI-6115	NI-PCI-6281	NI-PCle-7851R_RMIO	NI-PXI-6224
NI-PCI-6120	NI-PCI-6284		NI-PXI-6225
NI-PCI-6122	NI-PCI-6289	NI-PCle-7852R_RMIO	NI-PXI-6229
NI-PCI-6123	NI-PCI-7811R	NI-PCle-GPIB	NI-PXI-6230
NI-PCI-6132	NI-PCI-7813R	NI-PCle-GPIB/LP	NI-PXI-6232
NI-PCI-6133	NI-PCI-7830R_RMIO	NI-PCle-GPIB+	NI-PXI-6233
NI-PCI-6143		NI-PCle-GPIB+/LP	NI-PXI-6236
NI-PCI-6154	NI-PCI-7831R_RMIO	NI-PCI-GPIB	NI-PXI-6238
NI-PCI-6220	NI-PCI-7833R_RMIO	NI-PCI-GPIB/LP	NI-PXI-6239
NI-PCI-6221		NI-PCI-GPIB+	NI-PXI-6250
NI-PCI-6221(37-Pin)	NI-PCI-8232	NI-PCMCIA-GPIB	NI-PXI-6251
NI-PCI-6224	NI-PCle-6251	NI-PMC-GPIB	NI-PXI-6254
NI-PCI-6225	NI-PCle-6259	NI-PXI-6030E	NI-PXI-6255
NI-PCI-6229	NI-PCle-6320	NI-PXI-6040E	NI-PXI-6259
NI-PCI-6230	NI-PCle-6321	NI-PXI-6052E	NI-PXI-6280
NI-PCI-6232	NI-PCle-6323	NI-PXI-6070E	NI-PXI-6281
NI-PCI-6233	NI-PCle-6341	NI-PXI-6115	NI-PXI-6284
NI-PCI-6236	NI-PCle-6343	NI-PXI-6120	NI-PXI-6289
NI-PCI-6238	NI-PCle-6351	NI-PXI-6122	NI-PXI-7811R
NI-PCI-6239	NI-PCle-6353	NI-PXI-6123	NI-PXI-7813R
NI-PCI-6250	NI-PCle-6361	NI-PXI-6132	NI-PXI-7830R_RMIO
NI-PCI-6254	NI-PCle-6363		NI-PXI-7831R_RMIO

Multisim 14.1 Base Edition Components

NI-PXI-7833R_RMIO	NI-SCXI-1127_Independent	NI-USB-6289(Mass.Term.)	NJM022L
NI-PXI-7841R_RMIO			NJM022M
NI-PXI-7842R_RMIO	NI-SCXI-1127_Matrix	NI-USB-7845R_MIO	NJM062D
NI-PXI-7851R_RMIO		NI-USB-7846R_MIO	NJM062L
NI-PXI-7852R_RMIO	NI-SCXI-1128_1-Wire	NI-USB-7855R_MIO	NJM062M
NI-PXI-7853R_RMIO		NI-USB-7856R_MIO	NJM062V
NI-PXI-7854R_RMIO	NI-SCXI-1128_2-Wire	NI-USB-78xxR_DIO	NJM064D
NI-PXI-8232		NJD1718T4G	NJM064M
	NI-SCXI-1128_4-Wire	NJD2873T4G	NJM064V
NI-PXIe-6124	NI-SCXI-1128_Independent	NJD35N04G	NJM072BD
NI-PXIe-6341		NJD35N04T4G	NJM072BL
NI-PXIe-6356	NI-SCXI-1128_Matrix	NJL0281D	NJM072BM
NI-PXIe-6358	NI-SCXI-1160	NJL0281DG	NJM072BV
NI-PXIe-6361	NI-SCXI-1163R	NJL0302D	NJM072D
NI-PXIe-6363	NI-USB-6212(Mass.Term.)	NJL0302DG	NJM072L
NI-PXIe-6366		NJL1302DG	NJM072M
NI-PXIe-6368	NI-USB-6216(Mass.Term.)	NJL3281DG	NJM074D
NI-PXI-GPIB		NJL4281D	NJM074M
NI-sbRIO-9605	NI-USB-6225(Mass.Term.)	NJL4281DG	NJM074V
NI-sbRIO-9606		NJL4302D	NJM082BD
NI-sbRIO-9651	NI-USB-6251(Mass.Term.)	NJL4302DG	NJM082BL
NI-SCXI-1127_1-Wire	NI-USB-6255(Mass.Term.)	NJM022BD	NJM082BM
		NJM022BL	NJM082BV
NI-SCXI-1127_2-Wire	NI-USB-6259(Mass.Term.)	NJM022BM	NJM082D
		NJM022D	NJM082L
NI-SCXI-1127_4-Wire	NI-USB-6281(Mass.Term.)		

Multisim 14.1 Base Edition Components

NJM082V	NJM2082D	NJM2904D	NJM4250D
NJM084D	NJM2082L	NJM2904L	NJM4250M
NJM084M	NJM2082M	NJM2904M	NJM4565D
NJM084V	NJM2097M	NJM2904V	NJM4565L
NJM13600D	NJM2100D	NJM318D	NJM4565M
NJM13600M	NJM2100L	NJM318M	NJM4565V
NJM13700D	NJM2100M	NJM324D	NJM4580D
NJM13700M	NJM2100V	NJM324M	NJM4580E
NJM1458D	NJM2107F	NJM3403AD	NJM4580L
NJM1458M	NJM2114D	NJM3403AM	NJM4741D
NJM2041D	NJM2114L	NJM3403AV	NJM4741M
NJM2041L	NJM2115D	NJM3404AD	NJM5532D
NJM2041M	NJM2115L	NJM3404AL	NJM5532L
NJM2043D	NJM2115M	NJM3404AM	NJM5532M
NJM2043L	NJM2120D	NJM3414D	NJM5534D
NJM2043M	NJM2120L	NJM3414L	NJM5534M
NJM2058D	NJM2120M	NJM3414M	NJM741D
NJM2058M	NJM2121D	NJM3415D	NJM741E
NJM2059D	NJM2121L	NJM3415L	NJM741M
NJM2059M	NJM2121M	NJM3415M	NJMOP-07D
NJM2060D	NJM2900M	NJM3416V	NJMOP-07M
NJM2060M	NJM2900N	NJM353D	NJT4030PT1G
NJM2068D	NJM2902M	NJM353M	NJT4030PT3G
NJM2068L	NJM2902N	NJM3900M	NJT4031NT1G
NJM2068M	NJM2902V	NJM3900N	NJT4031NT3G

Multisim 14.1 Base Edition Components

NJV4030PT1G	NJVMJD44H11T4G	NOR4	NRVB1045MFST1G
NJV4030PT3G	NJVMJD45H11RLG	NOR4	NRVB1045MFST3G
NJV4031NT1G	NJVMJD45H11T4G	NOR5	NRVB120ESFT1G
NJV4031NT3G	NJVMJD50T4G	NOR5	NRVB120ESFT3G
NJVMJB41CT4G	NJVMJD6039T4G	NOR6	NRVB120LSFT1G
NJVMJB42CT4G	NJVNJD2873T4G	NOR6	NRVB1240MFST1G
NJVMJB44H11T4G	NJVNJD35N04G	NOR7	NRVB1240MFST3G
NJVMJB45H11T4G	NJVNJD35N04T4G	NOR7	NRVB130T1G
NJVMJD112T4G	NJW0281G	NOR8	NRVB140ESFT1G
NJVMJD117T4G	NJW0302G	NOR8	NRVB140ESFT3G
NJVMJD210T4G	NJW1302G	NOT	NRVB140SFT1G
NJVMJD243T4G	NJW21193G	NPD5564	NRVB140SFT3G
NJVMJD253T4G	NJW21194G	NPD5565	NRVB1H100SFT3G
NJVMJD2955T4G	NJW3281G	NPD5566	NRVB2045EMFST1G
NJVMJD3055T4G	NJX1675PDR2G	NPD8301	NRVB2045EMFST3G
NJVMJD31T4G	NLT_VIRTUAL	NPD8303	NRVB2045EMFST1G
NJVMJD32CG	NMOSFET_Thermal	NRVA4004T3G	NRVB2H100SFT3G
NJVMJD32CT4G	NO_CONTACT	NRVB0530T1G	NRVB30H100MFST1G
NJVMJD32T4G	NON_IDEAL_BATTERY	NRVB0530T3G	NRVB30H100MFST3G
NJVMJD350T4G	NONLINEAR_DEPENDENT	NRVB0540T1G	NRVB440MFST1G
NJVMJD42CRLG		NRVB0540T3G	NRVB440MFST3G
NJVMJD42CT4G	NOR2	NRVB10100G	NRVB440MFST1G
NJVMJD44E3T4G	NOR2	NRVB10100MFST1G	NRVB440MFST3G
NJVMJD44H11G	NOR3	NRVB10100MFST3G	NRVB440MFSWFT1G
NJVMJD44H11RLG	NOR3		

Multisim 14.1 Base Edition Components

NRVB440MFSWFT3 G	NRVBB2535CTLG	NRVBS240LT3G	NRVTS560EMFST3G
NRVB460MFST1G	NRVBB2535CTLT4G	NRVBS260T3G	NRVTS860EMFST1G
NRVB460MFST3G	NRVBB3030CTLG	NRVBS3100T3G	NRVTS860EMFST3G
NRVB5100MFST1G	NRVBB3030CTLT4G	NRVBS3200T3G	NRVTS44100ET3G
NRVB5100MFST3G	NRVBB30H60CTT4G	NRVBS3201T3G	NRVTS4F5100ET3G
NRVB540MFST1G	NRVBB4030T4G	NRVBS330T3G	NRVTS260ET1G
NRVB540MFST3G	NRVBB41H100CTT4 G	NRVBS360T3G	NRVTS260ET3G
NRVB560MFST1G	NRVBBS20100CTT4 G	NRVBS4201T3G	NRVTS3100ET3G
NRVB560MFST3G	NRVBD1035CTLT4G	NRVBS540T3G	NRVTS5100ET3G
NRVB5H100MFST1 G	NRVBD640CTG	NRVS1504T3G	NRVUB1620CTRT4G
NRVB8H100MFST1 G	NRVBD640CTT4G	NRVTS1045EMFST1 G	NRVUB1620CTT4G
NRVB8H100MFST3 G	NRVBD650CTT4G	NRVTS1045EMFST3 G	NRVUB1660CTT4G
NRVBA130LT3G	NRVBD660CTG	NRVTS1260EMFST1 G	NRVUD550PFT4G
NRVBA160T3G	NRVBD660CTT4G	NRVTS1260EMFST3 G	NRVUD620CTG
NRVBA1H100T3G	NRVBM110ET1G	NRVTS1545EMFST1 G	NRVUD620CTT4G
NRVBA210LT3G	NRVBM110LT1G	NRVTS1545EMFST3 G	NRVUS230T3G
NRVBA2H100T3G	NRVBM110LT3G	NRVTS245ESFT1G	NRVUS240T3G
NRVBA340T3G	NRVBM120ET1G	NRVTS245ESFT3G	NS32FV16-20
NRVBB1060T4G	NRVBM120ET3G	NRVTS260ESFT1G	NS32FV16-25
NRVBB20100CTT4G	NRVBM130LT1G	NRVTS260ESFT3G	NS32FX161-15
NRVBB2060CTT4G	NRVBM130LT3G	NRVTS260ESFT1G	NS32FX161-20
NRVBB20H100CTT4 G	NRVBM140T1G	NRVTS260ESFT3G	NS32FX164-20
	NRVBS2040LT3G	NRVTS560EMFST1G	NS32FX164-25
			NSA5.0AT3G
			NSB12ANT3G

Multisim 14.1 Base Edition Components

NSB4904DW1T1G	NSBA143ZDP6T5G	NSBC114YPDXV6T1G	NSBC143ZDP6T5G
NSB8MT-E3/81	NSBA143ZF3T5G		NSBC143ZDXV6T1G
NSB9435T1G	NSBA144EDP6T5G	NSBC114YPDXV6T5G	NSBC143ZF3T5G
NSBA114EDP6T5G	NSBA144EDXV6T1G	NSBC115EDXV6T1G	NSBC143ZPDP6T5G
NSBA114EDXV6T1G	NSBA144EF3T5G	NSBC115TDP6T5G	NSBC143ZPDXV6T1G
NSBA114EF3T5G	NSBA144TF3T5G	NSBC115TF3T5G	NSBC144EDP6T5G
NSBA114TDP6T5G	NSBA144WDP6T5G	NSBC115TPDP6T5G	NSBC144EDXV6T1G
NSBA114TF3T5G	NSBA144WF3T5G	NSBC123EF3T5G	NSBC144EDXV6T5G
NSBA114YDP6T5G	NSBC113EF3T5G	NSBC123JDP6T5G	NSBC144EF3T5G
NSBA114YDXV6T1G	NSBC114EDP6T5G	NSBC123JF3T5G	NSBC144EPDP6T5G
NSBA115EDXV6T1G	NSBC114EDXV6T1G	NSBC123JPDP6T5G	NSBC144EPDXV6T1G
NSBA115TDP6T5G	NSBC114EDXV6T5G	NSBC123JPDXV6T1G	NSBC144TF3T5G
NSBA115TF3T5G	NSBC114EF3T5G		NSBC144WDP6T5G
NSBA123EF3T5G	NSBC114EPDP6T5G	NSBC123TDP6T5G	NSBC144WF3T5G
NSBA123JDP6T5G	NSBC114EPDXV6T1G	NSBC123TF3T5G	NSD16F3T5G
NSBA123JDXV6T5G	G	NSBC124EDP6T5G	NSD914F3T5G
NSBA123JF3T5G	NSBC114EPDXV6T5G	NSBC124EDXV6T1G	NSDEMP11XV6T1G
NSBA123TDP6T5G	G	NSBC124EF3T5G	NSDEMP11XV6T5G
NSBA123TF3T5G	NSBC114TDP6T5G	NSBC124EPDXV6T1G	NSL12AWT1G
NSBA124EDP6T5G	NSBC114TDXV6T1G	G	NSM80100MT1G
NSBA124EF3T5G	NSBC114TF3T5G	NSBC124XF3T5G	NSM80101MT1G
NSBA124XF3T5G	NSBC114YDP6T5G	NSBC143EDP6T5G	NSPM1041BMUTB
NSBA143EDP6T5G	NSBC114YDXV6T1G	NSBC143EF3T5G	G
NSBA143EF3T5G	NSBC114YDXV6T5G	NSBC143TF3T5G	NSR0130P2T5G
NSBA143TF3T5G	NSBC114YF3T5G	NSBC143TPDXV6T1G	
	NSBC114YPDP6T5G	G	

Multisim 14.1 Base Edition Components

NSR0140P2T5G	NSR0620P2T5G	NSS12500UW3T2G	NSS40300DDR2G
NSR01F30MXT5G	NSR1020MW2T1G	NSS12501UW3T2G	NSS40300MDR2G
NSR01F30NXT5G	NSR1020MW2T3G	NSS12601CF8T1G	NSS40300MZ4T1G
NSR01L30MXT5G	NSR10404NXT5G	NSS1C200LT1G	NSS40301MDR2G
NSR01L30NXT5G	NSR10F20NXT5G	NSS1C200MZ4T1G	NSS40301MZ4T1G
NSR0230P2T5G	NSR10F30NXT5G	NSS1C200MZ4T3G	NSS40302PDR2G
NSR0240HT1G	NSR10F40NXT5G	NSS1C201LT1G	NSS40500UW3T2G
NSR0240P2T5G	NSR15304NXT5G	NSS1C201MZ4T1G	NSS40501UW3T2G
NSR0240V2T1G	NSR15405NXT5G	NSS1C201MZ4T3G	NSS40600CF8T1G
NSR02F30MXT5G	NSR15406NXT5G	NSS1C300ET4G	NSS40601CF8T1G
NSR02F30NXT5G	NSR20204NXT5G	NSS1C301ET4G	NSS60100DMTTBG
NSR02L30NXT5G	NSR20206NXT5G	NSS20200LT1G	NSS60101DMTTBG
NSR0320MW2T1G	NSR20305NXT5G	NSS20201LT1G	NSS60200LT1G
NSR0320MW2T3G	NSR20306NXT5G	NSS20300MR6T1G	NSS60201LT1G
NSR0320XV6T1G	NSR20406NXT5G	NSS20500UW3T2G	NSS60600MZ4T1G
NSR0320XV6T5G	NSR20F20NXT5G	NSS20501UW3T2G	NSS60601MZ4T1G
NSR0340HT1G	NSR20F30NXT5G	NSS20601CF8T1G	NST30010MXV6T1 G
NSR0340P2T5G	NSR30CM3T5G	NSS30100LT1G	NST3904DXV6T1G
NSR0340V2T1G	NSRLV20MW2T1G	NSS30101LT1G	NST3904DXV6T5G
NSR0520V2T1G	NSS12100M3T5G	NSS30201MR6T1G	NST3904F3T5G
NSR05F20NXT5G	NSS12100UW3TCG	NSS35200CF8T1G	NST3906DXV6T1G
NSR05F30NXT5G	NSS12100XV6T1G	NSS35200MR6T1G	NST3906F3T5G
NSR05F40NXT5G	NSS12200LT1G	NSS40200LT1G	NST3946DXV6T1G
NSR05T40P2T5G	NSS12200WT1G	NSS40200UW6T1G	NST3946DXV6T5G
NSR05T40XV2T5G	NSS12201LT1G	NSS40201LT1G	

Multisim 14.1 Base Edition Components

NST846BF3T5G	NSVB123JPDXV6T1 G	NSVMUN5212DW1 T1G	NTB6410ANG
NST847BF3T5G			NTB6410ANT4G
NST848BF3T5G	NSVB143ZPDXV6T1 G	NSVMUN5314DW1 T3G	NTB6411ANG
NST856BF3T5G	NSVB144EPDXV6T1 G	NSVMUN5333DW1 T1G	NTB6411ANT4G
NST857BF3T5G			NTB6412ANG
NSTB1005DXV5T1G	NSVBA114YDXV6T1 G	NSVMUN5334DW1 T1G	NTB6412ANT4G
NSTR4501NT1G	NSVBAT54LT1G	NSVT30010MXV6T1 G	NTB6413ANG
NSV1C300ET4G	NSVBAT54WT1G		NTB6413ANT4G
NSV1C301ET4G	NSVBAV70TT1G	NSVT3904DXV6T1G	NTB75N03L09T4G
NSV20200LT1G	NSVBAV70TT3G	NSVT65010MW6T1 G	NTB75N06T4G
NSV20201LT1G	NSVBC124EDXV6T1 G	NSVT65011MW6T1 G	NTBV5605T4G
NSV40200LT1G			NTD110N02RT4G
NSV40201LT1G	NSVBCP56-10T3G	NTA4001NT1G	NTD12N10-1G
NSV40300MDR2G	NSVBCP69T1G	NTA4151PT1G	NTD12N10T4G
NSV40300MZ4T1G	NSVJ3557SA3T1G	NTA4153NT1G	NTD14N03RT4G
NSV40301MZ4T1G	NSVMMBD353LT1G	NTA7002NT1G	NTD18N06LT4G
NSV60100DMTWTB G	NSVMMBT589LT1G	NTB25P06T4G	NTD18N06T4G
NSV60101DMTWTB G	NSVMMBT10LT1G	NTB30N06LT4G	NTD20N03L27T4G
	NSVMMUN2132LT1 G	NTB30N20T4G	NTD20N06T4G
NSV60600MZ4T1G		NTB45N06LT4G	NTD20P06LG
NSV60600MZ4T3G	NSVMMUN2232LT1 G	NTB45N06T4G	NTD20P06LT4G
NSV60601MZ4T1G	NSVMUN2212T1G	NTB5404NT4G	NTD24N06LT4G
NSV60601MZ4T3G	NSVMUN2233T1G	NTB5405NT4G	NTD24N06T4G
NSV9435T1G	NSVMUN5131T1G	NTB5605PT4G	NTD2955-1G
	NSVMUN5132T1G	NTB60N06T4G	NTD2955G

Multisim 14.1 Base Edition Components

NTD2955T4G	NTD4813N-35G	NTD4906N-1G	NTD4970N-35G
NTD3055-094-1G	NTD4813NH-1G	NTD4906N-35G	NTD4970NT4G
NTD3055-094T4G	NTD4813NH-35G	NTD4906NT4G	NTD5406NT4G
NTD3055-150T4G	NTD4813NHT4G	NTD4909N-1G	NTD5407NT4G
NTD3055L104-1G	NTD4813NT4G	NTD4909N-35G	NTD5802NT4G
NTD3055L104G	NTD4815N-35G	NTD4909NT4G	NTD5803NT4G
NTD3055L104T4G	NTD4815NT4G	NTD4910N-1G	NTD5804NT4G
NTD3055L170T4G	NTD4855NT4G	NTD4910N-35G	NTD5805NT4G
NTD32N06LT4G	NTD4856NT4G	NTD4910NT4G	NTD5806NT4G
NTD40N03RT4G	NTD4857NT4G	NTD4913N-1G	NTD5807NT4G
NTD4302T4G	NTD4858N-35G	NTD4913N-35G	NTD5865NL-1G
NTD4804NT4G	NTD4858NT4G	NTD4913NT4G	NTD5865NLT4G
NTD4805N-1G	NTD4860N-35G	NTD4960N-1G	NTD5867NL-1G
NTD4805NT4G	NTD4860NT4G	NTD4960N-35G	NTD5867NLT4G
NTD4806N-35G	NTD4863N-35G	NTD4960NT4G	NTD6414AN-1G
NTD4806NT4G	NTD4863NAT4G	NTD4963N-1G	NTD6414ANT4G
NTD4808N-1G	NTD4863NT4G	NTD4963N-35G	NTD6415AN-1G
NTD4808NT4G	NTD4863NT4H	NTD4963NT4G	NTD6415ANT4G
NTD4809N-35G	NTD4865NT4G	NTD4965N-1G	NTD6416AN-1G
NTD4809NH-1G	NTD4904N-1G	NTD4965N-35G	NTD6416ANL-1G
NTD4809NH-35G	NTD4904N-35G	NTD4965NT4G	NTD6416ANLT4G
NTD4809NHT4G	NTD4904NT4G	NTD4969N-1G	NTD6416ANT4G
NTD4809NT4G	NTD4905N-1G	NTD4969N-35G	NTD6600NT4G
NTD4810N-35G	NTD4905N-35G	NTD4969NT4G	NTD70N03R-1G
NTD4810NT4G	NTD4905NT4G	NTD4970N-1G	NTD70N03RT4G

Multisim 14.1 Base Edition Components

NTDV20N06T4G	NTHD3100CT1G	NTJS4151PT1G	NTLUS3A40PZTAG
NTE4151PT1G	NTHD3101FT1G	NTJS4160NT1G	NTLUS3A40PZTBG
NTE4153NT1G	NTHD3102CT1G	NTJS4405NT1G	NTLUS3A90PZTAG
NTF2955T1G	NTHD3133PFT1G	NTK3043NT1G	NTLUS3A90PZTBG
NTF3055-100T1G	NTHD4102PT1G	NTK3134NT1G	NTMD3P03R2G
NTF3055-100T3G	NTHD4502NT1G	NTK3134NT5G	NTMD4184PFR2G
NTF3055L108T1G	NTHD4508NT1G	NTK3139PT1G	NTMD4820NR2G
NTF3055L175T1G	NTHD4P02FT1G	NTK3139PT5G	NTMD4840NR2G
NTF5P03T3G	NTHS4101PT1G	NTK3142PT1G	NTMD4884NFR2G
NTF6P02T3G	NTHS4166NT1G	NTLGD3502NT2G	NTMD4N03R2G
NTGD1100LT1G	NTHS5404T1G	NTLGF3402PT2G	NTMD5836NLR2G
NTGD3149CT1G	NTHS5441T1G	NTLJD3115PT1G	NTMD5838NLR2G
NTGD4161PT1G	NTHS5443T1G	NTLJD3119CTAG	NTMD6N02R2G
NTGD4167CT1G	NTJD1155LT1G	NTLJD3119CTBG	NTMD6P02R2G
NTGS3130NT1G	NTJD4001NT1G	NTLJD4116NT1G	NTMFS4108NT1G
NTGS3136PT1G	NTJD4105CT1G	NTLJF3117PT1G	NTMFS4119NT1G
NTGS3441PT1G	NTJD4105CT2G	NTLJF4156NT1G	NTMFS4744NT1G
NTGS3441T1G	NTJD4152PT1G	NTLJF4156NTAG	NTMFS4821NT1G
NTGS3443T1G	NTJD4158CT1G	NTLJS2103PTBG	NTMFS4823NT1G
NTGS3446T1G	NTJD4158CT2G	NTLJS3113PT1G	NTMFS4823NT3G
NTGS4111PT1G	NTJD4401NT1G	NTLJS3113PTAG	NTMFS4825NFET1G
NTGS4141NT1G	NTJD5121NT1G	NTLJS4114NT1G	NTMFS4825NFET3G
NTGS5120PT1G	NTJD5121NT2G	NTLUD3A260PZTAG	NTMFS4833NT1G
NTHC5513T1G	NTJS3151PT1G	NTLUD3A260PZTBG	NTMFS4833NT3G
NTHD2102PT1G	NTJS3157NT1G	NTLUF4189NZTAG	NTMFS4834NT1G

Multisim 14.1 Base Edition Components

NTMFS4835NT1G	NTMFS4923NET3G	NTMFS4945NT1G	NTP2955G
NTMFS4836NT1G	NTMFS4925NET1G	NTMFS5830NLT1G	NTP35N15G
NTMFS4837NHT1G	NTMFS4925NET3G	NTMS10P02R2G	NTR0202PLT1G
NTMFS4839NHT1G	NTMFS4925NT1G	NTMS4176PR2G	NTR1P02LT1G
NTMFS4841NHT1G	NTMFS4925NT3G	NTMS4177PR2G	NTR1P02LT3G
NTMFS4841NT1G	NTMFS4926NET1G	NTMS4503NR2G	NTR2101PT1G
NTMFS4845NT1G	NTMFS4926NET3G	NTMS4800NR2G	NTR3161NT1G
NTMFS4846NT1G	NTMFS4926NT1G	NTMS4801NR2G	NTR3162PT1G
NTMFS4847NAT1G	NTMFS4926NT3G	NTMS4802NR2G	NTR4003NT1G
NTMFS4847NAT3G	NTMFS4927NT1G	NTMS4807NR2G	NTR4003NT3G
NTMFS4847NT1G	NTMFS4927NT3G	NTMS4816NR2G	NTR4101PT1G
NTMFS4851NT1G	NTMFS4934NT1G	NTMS4840NR2G	NTR4170NT1G
NTMFS4852NT1G	NTMFS4934NT3G	NTMS4872NR2G	NTR4171PT1G
NTMFS4852NT3G	NTMFS4935NT1G	NTMS4873NFR2G	NTR4501NT1G
NTMFS4897NFT1G	NTMFS4935NT3G	NTMS4916NR2G	NTR4502PT1G
NTMFS4897NFT3G	NTMFS4936NT1G	NTMS4917NR2G	NTR4502PT3G
NTMFS4898NFT1G	NTMFS4936NT3G	NTMS4920NR2G	NTR4503NT1G
NTMFS4898NFT3G	NTMFS4937NT1G	NTMS4935NR2G	NTS1045MFST1G
NTMFS4899NFT1G	NTMFS4937NT3G	NTMS4937NR2G	NTS1045MFST3G
NTMFS4899NFT3G	NTMFS4939NT1G	NTMS4939NR2G	NTS1260MFST1G
NTMFS4921NT1G	NTMFS4939NT3G	NTMS5835NLR2G	NTS1260MFST3G
NTMFS4921NT3G	NTMFS4941NT1G	NTMS5838NLR2G	NTS1545MFST1G
NTMFS4922NET1G	NTMFS4941NT3G	NTMS5P02R2G	NTS1545MFST3G
NTMFS4922NET3G	NTMFS4943NT1G	NTNS3A65PZT5G	NTS2101PT1G
NTMFS4923NET1G	NTMFS4943NT3G	NTNUS3171PZT5G	NTS245SFT1G

Multisim 14.1 Base Edition Components

NTS245SFT3G	NTSJ30U80CTG	NTTFS4824NTAG	NTZD3155CT1G
NTS260SFT1G	NTSS3100T3G	NTTFS4840NTAG	NTZD3155CT2G
NTS260SFT3G	NTSS5100T3G	NTTFS4932NTAG	NTZD3155CT5G
NTS4001NT1G	NTST20100CTG	NTTFS4932NTWG	NTZD5110NT1G
NTS4101PT1G	NTST20120CTG	NTTFS4937NTAG	NTZS3151PT1G
NTS4173PT1G	NTST20U100CTG	NTTFS4937NTWG	NUP1105LT1G
NTS4409NT1G	NTST30100CTG	NTTFS4939NTAG	NUP1301
NTS560MFST1G	NTST30100CTH	NTTFS4939NTWG	NUP1301ML3T1G
NTS560MFST3G	NTST30100SG	NTTFS4941NTAG	NUP1301U
NTS860MFST1G	NTST30120CTG	NTTFS4941NTWG	NUP2105LT1G
NTS860MFST3G	NTST30U100CTG	NTTFS4943NTAG	NUP2202W1T2G
NTSA4100T3G	NTST30U100CTH	NTTFS4945NTAG	NUP4102XV6T1G
NTSAF345T3G	NTST40120CTG	NTTFS5811NLTAG	NUP4103FCT1G
NTSAF5100T3G	NTST40120CTH	NTTFS5811NLTWG	NUP4201DR2G
NTSAF545T3G	NTSV20100CTG	NTTFS5820NLTAG	NUP4201MR6T1G
NTSB20100CT-1G	NTSV20120CTG	NTTFS5820NLTWG	NUP4202W1T2G
NTSB20U100CT-1G	NTSV20U100CTG	NTUD3127CT5G	NUP4301MR6T1G
NTSB30100CT-1G	NTSV30100CTG	NTUD3128NT5G	NUP4302MR6T1G
NTSB30100S-1G	NTSV30120CTG	NTUD3169CZT5G	NUP4304MR6T1G
NTSB30U100CT-1G	NTTD4401FR2G	NTUD3170NZT5G	NUP45V6P5T5G
NTSJ20100CTG	NTTFS4800NTAG	NTUD3171PZT5G	NUS3116MTR2G
NTSJ2080CTG	NTTFS4821NTAG	NTZD3152PT1G	NVB6413ANT4G
NTSJ20U100CTG	NTTFS4821NTWG	NTZD3154NT1G	NVD4804NT4G
NTSJ30100CTG	NTTFS4823NTAG	NTZD3154NT2G	NVD5117PLT4G
NTSJ3080CTG	NTTFS4823NTWG	NTZD3154NT5G	NVD5802NT4G

Multisim 14.1 Base Edition Components

NVD5807NT4G	NX3008NBKS	NZH15B	NZQA5V6XV5T1G
NVD5865NLT4G	NX3008NBKT	NZH16C	NZQA6V8AXV5T1G
NVD5890NT4G	NX3008NBKV	NZH18C	NZQA6V8AXV5T2G
NVDD5894NLT4G	NX3008NBKW	NZH20C	NZQA6V8AXV5T3G
NVF2955T1G	NX3008PBK	NZH22C	NZX10A
NVF3055-100T1G	NX3008PBKMB	NZH24C	NZX10C
NVF3055L108T1G	NX3008PBKS	NZH27C	NZX11A
NVF3055L108T3G	NX3008PBKT	NZH30C	NZX11C
NVF5P03T3G	NX3008PBKV	NZH3V0B	NZX11D
NVF6P02T3G	NX3008PBKW	NZH3V3A	NZX12A
NVMD3P03R2G	NX7002AK	NZH3V6B	NZX12B
NVMS4816NR2G	NX7002AKS	NZH3V9B	NZX12C
NVTA7002NT1G	NX7002AKW	NZH4V3B	NZX12D
NVTFS4824NTAG	NX7002BK	NZH4V7B	NZX13B
NVTFS4824NTWG	NXP3875G	NZH5V1B	NZX13C
NVTFS5826NLTAG	NXP3875Y	NZH5V6B	NZX14A
NVTFS5826NLTWG	NZ9F2V4ST5G	NZH6V2B	NZX14B
NVTJD4001NT1G	NZ9F2V4T5G	NZH6V8B	NZX14C
NVTR01P02LT1G	NZ9F2V7ST5G	NZH7V5C	NZX15B
NVTR0202PLT1G	NZ9F5V1T5G	NZH8V2B	NZX16A
NVTR4502PT1G	NZ9F6V2ST5G	NZH9V1B	NZX16B
NVTR4503NT1G	NZH10C	NZL5V6ATT1G	NZX16C
NX2301P	NZH11C	NZL5V6AXV3T1G	NZX18A
NX3008NBK	NZH12B	NZL6V8AXV3T1G	NZX18B
NX3008NBKMB	NZH13B	NZL7V5AXV3T1G	NZX18C

Multisim 14.1 Base Edition Components

NZX20A	NZX5V1C	OP01J	OP05H
NZX20B	NZX5V1D	OP02AJ	OP05J
NZX22A	NZX5V6A	OP02AZ	OP05J8
NZX22B	NZX5V6B	OP02CJ	OP06AJ
NZX24A	NZX5V6C	OP02CP	OP06GJ
NZX24B	NZX5V6D	OP02CZ	OP06GZ
NZX27A	NZX5V6E	OP04AK	OP07AH
NZX27B	NZX6V2B	OP04AY	OP07AJ
NZX27C	NZX6V2C	OP04EY	OP07AJ8
NZX2V4A	NZX6V2D	OP05AH	OP07AZ
NZX2V7B	NZX6V2E	OP05AJ	OP07CD
NZX30A	NZX6V8A	OP05AJ8	OP07CH
NZX30C	NZX6V8B	OP05AZ	OP07CJ8
NZX33C	NZX6V8C	OP05CH	OP07CJG
NZX36C	NZX7V5A	OP05CJ	OP07CN8
NZX3V0B	NZX7V5B	OP05CJ8	OP07CP
NZX3V3B	NZX7V5D	OP05CN8	OP07CS8
NZX3V3C	NZX8V2A	OP05CP	OP07DD
NZX3V6C	NZX8V2B	OP05CZ	OP07DJG
NZX3V9C	NZX8V2D	OP05EH	OP07DP
NZX4V3C	NZX9V1B	OP05EJ	OP07ED
NZX4V7A	NZX9V1E	OP05EJ8	OP07EH
NZX4V7C	OCTAL_REG	OP05EN8	OP07EJ8
NZX4V7D	OL	OP05EP	OP07EJG
NZX5V1B	OP01CZ	OP05EZ	OP07EN8

Multisim 14.1 Base Edition Components

OP07EP	OP12EZ	OP160GS	OP176GS
OP07H	OP15AH	OP162DRU	OP177AZ
OP07J	OP15AJ	OP162GS	OP177BRC/883
OP07J8	OP15AZ	OP162GSZ	OP177BZ
OP07RC/883	OP15BH	OP16AH	OP177EZ
OP07Y	OP15BJ/883	OP16AJ	OP177FP
OP07Z	OP15BZ/883	OP16BH	OP177FS
OP08	OP15CH	OP16BJ/883	OP177FZ
OP09AY	OP15EH	OP16BZ/883	OP177GP
OP09BY	OP15EJ	OP16C	OP177GS
OP10AY	OP15EZ	OP16CH	OP177GZ
OP10CY	OP15FH	OP16EH	OP183GP
OP10EY	OP15FJ	OP16EJ	OP183GS
OP10Y	OP15FP	OP16EZ	OP184ES
OP113EP	OP15FZ	OP16FH	OP191GP
OP113ES	OP15GH	OP16FJ	OP191GS
OP113FP	OP15GJ	OP16FP	OP193EP
OP113FS	OP15GN8	OP16FZ	OP193ES
OP1177AR	OP15GP	OP16GH	OP193FP
OP1177ARM	OP15GS	OP16GJ	OP193FS
OP11GP	OP15GZ	OP16GN8	OP196GP
OP11GS	OP160ARC/883	OP16GP	OP196GS
OP12BJ	OP160AZ	OP16GS	OP200AZ
OP12BZ/883	OP160FZ	OP16GZ	OP200EZ
OP12EJ	OP160GP	OP176GP	OP200FZ

Multisim 14.1 Base Edition Components

OP200GP	OP215AZ	OP2177ARMZ	OP221EZ
OP200GS	OP215BJ/883	OP2177ARZ	OP221GJ
OP207AY	OP215BRC/883	OP21AJ	OP221GP
OP207EY	OP215BZ/883	OP21AZ	OP221GS
OP207FY	OP215CH	OP21EZ	OP221GZ
OP20BJ	OP215CJ/883	OP21FJ	OP227AJ
OP20BZ	OP215CJ8	OP21FP	OP227CJ
OP20CZ	OP215CZ/883	OP21FZ	OP227EJ
OP20FP	OP215EH	OP21GJ	OP227EN
OP20GJ	OP215EJ	OP21GP	OP227GJ
OP20GP	OP215EJ8	OP21HS	OP227GN
OP20GZ	OP215EN8	OP220AJ	OP22AJ/883
OP20HJ	OP215EP	OP220AZ	OP22AZ
OP20HS	OP215EZ	OP220CJ	OP22HP
OP20HZ	OP215FJ	OP220CZ	OP22HS
OP213AZ/883	OP215FP	OP220EZ	OP22HZ
OP213BZ/883	OP215FZ	OP220FZ	OP237AJ
OP213EP	OP215GH	OP220GJ	OP237CJ
OP213ES	OP215GJ8	OP220GP	OP237EJ
OP213EZ	OP215GN8	OP220GS	OP237EN
OP213FP	OP215GP	OP220GZ	OP237GJ
OP213FS	OP215GS	OP221AJ/883	OP237GN
OP215AH	OP215GZ	OP221AZ	OP249AJ
OP215AJ	OP2177AR	OP221BJ	OP249ARC/883
OP215AJ8	OP2177ARM	OP221CJ	OP249AZ

Multisim 14.1 Base Edition Components

OP249EJ	OP27AH	OP27GJ	OP290FZ
OP249FJ	OP27AJ	OP27GJ8	OP290GP
OP249FZ	OP27AJ8	OP27GJZ	OP290GS
OP249GP	OP27AJG	OP27GN8	OP291GP
OP249GPZ	OP27AL	OP27GP	OP291GS
OP249GS	OP27AZ	OP27GPZ	OP292GP
OP249GSZ	OP27BJ	OP27GS	OP292GS
OP260AJ	OP27BR/883	OP27GSZ	OP293EP
OP260ARC/883	OP27BZ	OP27GZ	OP293ES
OP260GP	OP27CH	OP281GRU	OP293FP
OP260GS	OP27CJ	OP281GS	OP293FS
OP262DRU	OP27CJ8	OP282AZ/883	OP295A
OP262DRUZ-REEL	OP27CJG	OP282GP	OP295AP
OP262GS	OP27CZ	OP282GS	OP295GP
OP262GSZ	OP27EH	OP283GP	OP295GS
OP262HRUZ-REEL	OP27EJ	OP283GS	OP296GP
OP270EZ	OP27EJ8	OP284EP	OP296GS
OP270FZ	OP27EN8	OP284ES	OP296HRU
OP270GP	OP27EP	OP284FP	OP297ARC/883
OP270GS	OP27EPZ	OP284FS	OP297AZ
OP275GP	OP27EZ	OP285GP	OP297AZ/883
OP275GS	OP27FJ	OP285GS	OP297EZ
OP279GP	OP27FP	OP290ARC/883	OP297FP
OP279GS	OP27FZ	OP290AZ	OP297FZ
OP279HRU	OP27GH	OP290EZ	OP297GP

Multisim 14.1 Base Edition Components

OP297GS	OP37EJ8	OP413EY	OP421FY
OP32AZ	OP37EN8	OP413FP	OP421GP
OP32EP	OP37EP	OP413FS	OP421GS
OP32EZ	OP37EPZ	OP4177AR	OP421GY
OP32FP	OP37EZ	OP4177ARU	OP421HP
OP32FZ	OP37FJ	OP4177ARUZ	OP421HS
OP32GP	OP37FP	OP4177ARZ	OP421HY
OP32GZ	OP37FZ	OP41AJ	OP42AJ
OP37AFK	OP37GH	OP41BJ	OP42ARC/883
OP37AH	OP37GJ	OP41EJ	OP42AZ
OP37AJ	OP37GJ8	OP41FJ	OP42EJ
OP37AJ8	OP37GN8	OP41GP	OP42EZ
OP37AJG	OP37GP	OP41GS	OP42FJ
OP37AL	OP37GS	OP420BY	OP42FZ
OP37AZ	OP37GZ	OP420CRC/883	OP42GP
OP37BJ	OP400ATC/883	OP420CY	OP42GS
OP37BRC/883	OP400AY	OP420FY	OP43
OP37BZ	OP400EY	OP420GP	OP43A
OP37CH	OP400FY	OP420GS	OP43B
OP37CJ	OP400GP	OP420GY	OP43E
OP37CJ8	OP400GS	OP420HP	OP43F
OP37CJG	OP400HP	OP420HS	OP43G
OP37CZ	OP400HS	OP420HY	OP44AJ
OP37EH	OP413EP	OP421BY	OP462DRU
OP37EJ	OP413ES	OP421CY	OP462DRUZ-REEL

Multisim 14.1 Base Edition Components

OP462DS	OP484FS	OP497CY	OP747ARU
OP462GS	OP490ATC/883	OP497FP	OP777AR
OP462GSZ	OP490AY	OP497FS	OP777ARM
OP462HRU-REEL	OP490EY	OP497FY	OP77BJ
OP462HRUZ-REEL	OP490FY	OP497GP	OP77BRC/883
OP467ARC/883	OP490GP	OP497GS	OP77BZ
OP467AY/883	OP490GS	OP497GY	OP77EZ
OP467GP	OP491GP	OP50AY	OP77FJ
OP467GS	OP491GS	OP50BY	OP77FZ
OP470ARC/883	OP491GSZ	OP50EY	OP77GP
OP470ATC/883	OP492GP	OP50FY	OP77GS
OP470AY	OP492GS	OP61ARC/883	OP80BJ
OP470EY	OP493EP	OP61AZ	OP80EJ
OP470GP	OP493ES	OP61FZ	OP80FJ
OP470GS	OP493FP	OP61GP	OP80GP
OP481GRU	OP493FS	OP61GS	OP80GS
OP481GS	OP495GP	OP64AJ	OP906
OP482ARC/883	OP495GS	OP64ARC/883	OP90ARC/883
OP482AY/883	OP495GSZ	OP64AZ	OP90AZ
OP482GP	OP496GP	OP64GP	OP90EZ
OP482GPZ	OP496GS	OP64GS	OP90FZ
OP484EP	OP496HRU	OP727AR	OP90GP
OP484ES	OP497AY	OP727ARU	OP90GS
OP484FP	OP497BRC/883	OP727ARUZ	OP950
OP484FPZ	OP497BY	OP747AR	OP97AJ

Multisim 14.1 Base Edition Components

OP97AZ	OPA129P	OPA1642AIDGKR	OPA209AIDGKR
OP97EP	OPA129PB	OPA1642AIDR	OPA209AIDR
OP97FJ	OPA129U	OPA1644AID	OPA2107AM
OP97FP	OPA129UB	OPA1644AIPW	OPA2107AP
OP97FS	OPA131PA	OPA1688ID	OPA2107AU
OP97FZ	OPA131PJ	OPA177EZ	OPA2107BM
OP999	OPA131UA	OPA177FP	OPA2107SM
OPA1013CN8	OPA131UJ	OPA177FZ	OPA2111AM
OPA1013DN8	OPA137N	OPA177GP	OPA2111BM
OPA111AM	OPA137NA	OPA177GS	OPA2111KM
OPA111BM	OPA137P	OPA177GZ	OPA2111KP
OPA111SM	OPA137PA	OPA180ID	OPA2111SM
OPA121KM	OPA137U	OPA180IDBVR	OPA211AID
OPA121KP	OPA137UA	OPA180IDGKR	OPA211AIDGKR
OPA121KU	OPA140AID	OPA191ID	OPA211AIDR
OPA124P	OPA140AIDBVR	OPA191IDBVT	OPA211AIDRGR
OPA124PA	OPA140AIDGKR	OPA191IDGKT	OPA211ID
OPA124PB	OPA140AIDR	OPA192ID	OPA211IDGKR
OPA124U	OPA141AIDGKR	OPA192IDBVT	OPA211IDR
OPA124UA	OPA141AIDR	OPA192IDGKT	OPA211IDRGR
OPA124UB	OPA1612AID	OPA197ID	OPA2131PA
OPA128JM	OPA1622IDRCT	OPA197IDBVT	OPA2131PJ
OPA128KM	OPA1632D	OPA197IDGKT	OPA2131UA
OPA128LM	OPA1632DGN	OPA209AID	OPA2131UJ
OPA128SM	OPA1642AID	OPA209AIDBVR	OPA2134PA

Multisim 14.1 Base Edition Components

OPA2134UA	OPA2333AIDRBR	OPA234EA/250	OPA2376AIDGKR
OPA2140AID	OPA2333AIDRG4	OPA234P	OPA2376AIDR
OPA2140AIDGKR	OPA2334AIDGSR	OPA234PA	OPA2376AIYZDR
OPA2140AIDR	OPA2335AID	OPA234U	OPA2377AID
OPA2141AIDGKR	OPA2335AIDGKR	OPA234UA	OPA2377AIDGKR
OPA2141AIDR	OPA2335AIDR	OPA2350EA	OPA2377AIDR
OPA2209AID	OPA2337EA/250	OPA2350PA	OPA2378AIDCNR
OPA2209AIDGKR	OPA2337PA	OPA2350UA	OPA2379AID
OPA2209AIDR	OPA2337UA	OPA2353EA/250	OPA2379AIDCNR
OPA228P	OPA2338EA/250	OPA2353UA	OPA2379AIDG4
OPA228U	OPA2338UA	OPA2354AIDDA	OPA2380AIDGKR
OPA2300AIDGSR	OPA2343EA/250	OPA2354AIDGKR	OPA2381AIDGKR
OPA2301AID	OPA2343UA	OPA2355DGSA/250	OPA2381AIDRBT
OPA2301AIDGKR	OPA2344EA/250	OPA2357AIDGSR	OPA2541AM
OPA2301AIDR	OPA2344PA	OPA2363AIDGSR	OPA2541BM
OPA2316SIDGS	OPA2344UA	OPA2363AIRSVR	OPA2541SM
OPA2317ID	OPA2345EA/250	OPA2363IDGSR	OPA2541SMQ
OPA2317IDGKR	OPA2345UA	OPA2369AIDCNR	OPA2544T
OPA2330AID	OPA2347EA	OPA2369AIDGKR	OPA2604AP
OPA2330AIDGKR	OPA2347UA	OPA2373AIDGSR	OPA2604AU
OPA2330AIDR	OPA2349EA/250	OPA2373AIDRCR	OPA2613ID
OPA2330AIDRBR	OPA2349UA	OPA2374AID	OPA2613IDTJ
OPA2330AIDRG4	OPA234E	OPA2374AIDCNR	OPA2614ID
OPA2333AIDGKR	OPA234E/250	OPA2374AIDG4	OPA2614IDTJ
OPA2333AIDR	OPA234EA	OPA2376AID	OPA2626IDGKT

Multisim 14.1 Base Edition Components

OPA2652E	OPA2704UA	OPA27GP	OPA320SAIDBVR
OPA2652U	OPA2725AID	OPA27GU	OPA322AIDBVR
OPA2658P	OPA2725AIDGKR	OPA27GZ	OPA322SAIDBVR
OPA2658PB	OPA2725AIDR	OPA2822E/250	OPA333AID
OPA2658U	OPA2726AIDGST	OPA2822U	OPA333AIDBVR
OPA2658UB	OPA2727AID	OPA2835ID	OPA333AIDCKR
OPA2674I-14D	OPA2727AIDRBR	OPA2835IDGS	OPA333AIDG4
OPA2674ID	OPA2727AIDRG4	OPA2835IRMCR	OPA334AID
OPA2677T	OPA2735AID	OPA2835IRUNR	OPA3355EA/250
OPA2677U	OPA2735AIDGKR	OPA2836ID	OPA3355UA
OPA2683ID	OPA2735AIDR	OPA2836IDGS	OPA335AID
OPA2683IDCNR	OPA2743EA/250	OPA2836IRUNR	OPA335AIDBV
OPA2683IDG4	OPA2743PA	OPA2846ID	OPA336N/250
OPA2683IDGST	OPA2743UA	OPA2889IDGST	OPA336NA/250
OPA2684ID	OPA27AJ	OPA2890IDGST	OPA336NJ/250
OPA2684IDCNR	OPA27AZ	OPA300AID	OPA336U
OPA2690I-14D	OPA27BJ	OPA300AIDBV	OPA336UA
OPA2690ID	OPA27BZ	OPA301AID	OPA337EA/250
OPA2691I-14D	OPA27CJ	OPA301AIDBV	OPA337NA/250
OPA2691ID	OPA27CZ	OPA316IDBVR	OPA337PA
OPA2703EA/250	OPA27EJ	OPA316IDCKR	OPA337UA
OPA2703PA	OPA27EZ	OPA317ID	OPA338NA/250
OPA2703UA	OPA27FJ	OPA317IDBVR	OPA338UA
OPA2704EA/250	OPA27FZ	OPA317IDCKR	OPA343NA
OPA2704PA	OPA27GJ	OPA320AIDBVR	OPA343UA

Multisim 14.1 Base Edition Components

OPA344NA	OPA356AID	OPA377AIDCKR	OPA404AG
OPA344PA	OPA356AIDBVT	OPA377AIDR	OPA404BG
OPA344UA	OPA357AIDBV	OPA378AIDBVR	OPA404KP
OPA345NA	OPA3583AM	OPA378AIDCKR	OPA404KU
OPA345UA	OPA3583JM	OPA379AID	OPA404SG
OPA347NA	OPA358AIDCK	OPA379AIDBVR	OPA4131NA
OPA347PA	OPA360AIDCK	OPA379AIDCKR	OPA4131NJ
OPA347SA	OPA363ID	OPA379AIDG4	OPA4131PA
OPA347UA	OPA363IDBV	OPA37AJ	OPA4131PJ
OPA348AID	OPA364ID	OPA37AZ	OPA4131UA
OPA348AIDBV	OPA364IDBV	OPA37BJ	OPA4134UA
OPA348AIDCKR	OPA365AID	OPA37BZ	OPA4137P
OPA349NA	OPA365AIDBVR	OPA37CJ	OPA4137PA
OPA349SA	OPA3690ID	OPA37CZ	OPA4137U
OPA349UA	OPA3690IDBQR	OPA37EJ	OPA4137UA
OPA350EA	OPA3690IDG4	OPA37EZ	OPA4140AID
OPA350PA	OPA3693IDBQ	OPA37FJ	OPA4140AIPW
OPA350UA	OPA3695IDBQ	OPA37FZ	OPA4141AID
OPA353NA	OPA369AIDCKR	OPA37GJ	OPA4141AIPW
OPA353UA	OPA373AID	OPA37GP	OPA4209AIPW
OPA354AIDBV	OPA373AIDBV	OPA37GU	OPA4227PA
OPA354AIDDA	OPA374AID	OPA37GZ	OPA4227UA
OPA355NA	OPA374AIDBV	OPA380AID	OPA4228PA
OPA355QDBVRQ1	OPA377AID	OPA380AIDGK	OPA4228UA
OPA355UA	OPA377AIDBVR	OPA381AIDGK	OPA4241PA

Multisim 14.1 Base Edition Components

OPA4241UA	OPA4379AIPWR	OPA501RM	OPA561PWP
OPA4243EA	OPA445AP	OPA501SM	OPA564AIDWD
OPA4244EA	OPA445BM	OPA502BM	OPA564AIDWP
OPA4251PA	OPA445SM	OPA502SM	OPA567AIRHGR
OPA4251UA	OPA452TA	OPA511AM	OPA569AIDWP
OPA4277PA	OPA454AIDDA	OPA512BM	OPA600BM
OPA4277UA	OPA4650P	OPA512SM	OPA600CM
OPA4317ID	OPA4650PB	OPA541AM	OPA600SM
OPA4317IPW	OPA4650U	OPA541AP	OPA600TM
OPA4330AID	OPA4658P	OPA541BM	OPA602AM
OPA4330AIPW	OPA4658PB	OPA541SM	OPA602AP
OPA4330AIRGYR	OPA4658U	OPA544F	OPA602AU
OPA4342EA	OPA4658UB	OPA544T	OPA602BM
OPA4342PA	OPA4684ID	OPA547T	OPA602BP
OPA4342UA	OPA4684IPWT	OPA548T	OPA602CM
OPA4345UA	OPA4703EA/250	OPA549S	OPA602SM
OPA4347EA	OPA4703UA	OPA549T	OPA603AP
OPA4347UA	OPA4704EA/250	OPA551FA/500	OPA603AU
OPA4348AID	OPA4704UA	OPA551FAKTWT	OPA604AP
OPA4348AIP	OPA4743EA/250	OPA551PA	OPA604AU
OPA4354AID	OPA4743UA	OPA551UA	OPA606KM
OPA4354AIPWR	OPA4820ID	OPA552FA/500	OPA606KP
OPA4374AID	OPA4820IPWR	OPA552FAKTWT	OPA606LM
OPA4374AIPWR	OPA501AM	OPA552PA	OPA620KG
OPA4377AIPW	OPA501BM	OPA552UA	OPA620KP

Multisim 14.1 Base Edition Components

OPA620KU	OPA637AU	OPA643U	OPA653IDBVR
OPA620LG	OPA637BM	OPA643UB	OPA653IDRBR
OPA620SG	OPA637BP	OPA644U	OPA654AM
OPA621KG	OPA637SM	OPA644UB	OPA655H
OPA621KP	OPA640H	OPA646H	OPA655HSQ
OPA621KU	OPA640HSQ	OPA646HSQ	OPA655P
OPA621LG	OPA640P	OPA646P	OPA655PB
OPA621SG	OPA640U	OPA646PB	OPA655UB
OPA622AP	OPA640UB	OPA646U	OPA656N
OPA622AU	OPA641H	OPA646UB	OPA656U
OPA623AP	OPA641HSQ	OPA648H	OPA658N
OPA623AU	OPA641P	OPA648P	OPA658P
OPA625IDBVR	OPA641PB	OPA648U	OPA658U
OPA625IDBVT	OPA641U	OPA650N	OPA659IDBVR
OPA627AM	OPA641UB	OPA650NB	OPA659IDRBR
OPA627AP	OPA642H	OPA650P	OPA671AP
OPA627AU	OPA642HSQ	OPA650PB	OPA675JG
OPA627BM	OPA642P	OPA650U	OPA675KG
OPA627BP	OPA642PB	OPA650UB	OPA675SG
OPA627SM	OPA642U	OPA651N	OPA676JG
OPA628AP	OPA642UB	OPA651NB	OPA676KG
OPA628AU	OPA643H	OPA651P	OPA676SG
OPA633KP	OPA643HSQ	OPA651PB	OPA678AG
OPA637AM	OPA643P	OPA651U	OPA678AP
OPA637AP	OPA643PB	OPA651UB	OPA678AU

Multisim 14.1 Base Edition Components

OPA678SG	OPA699ID	OPA77GP	OR4
OPA680N	OPA703NA	OPA820ID	OR4
OPA680P	OPA703PA	OPA820IDBVR	OR5
OPA680U	OPA703UA	OPA820IDG4	OR5
OPA681N	OPA704NA	OPA827AID	OR6
OPA681P	OPA704PA	OPA827AIDGKR	OR6
OPA681U	OPA704UA	OPA830ID	OR7
OPA682N	OPA725AID	OPA830IDBVT	OR7
OPA682P	OPA725AIDBV	OPA835IDBVR	OR8
OPA682U	OPA726AID	OPA836IDBVR	OR8
OPA683BV	OPA726AIDGK	OPA842ID	OSTV7163151
OPA683ID	OPA727AIDGKR	OPA842IDBV	OSTV7203101
OPA684ID	OPA727AIDRBT	OPA847ID	OSTV7203151
OPA684IDBV	OPA728AIDGKT	OPA847IDBV	OVERLOAD
OPA686N	OPA728AIDRBT	OPA857IRGTR	P4KE10CA-E3/54
OPA686U	OPA734AID	OPAMP_3T_VIRTU AL	P4KE300A/3
OPA687N	OPA734AIDBV	OPAMP_5T_VIRTU AL	P4SMA36CA-E3/61
OPA687U	OPA735AID	OPT301M	P6KE100A-E3/54
OPA690ID	OPA735AIDBV	OPTOCOUPLER_VIR TUAL	P6KE10A-E3/54
OPA690IDBV	OPA743NA	OR2	P6KE200AG
OPA693ID	OPA743PA	OR2	P6KE200ARLG
OPA693IDBVT	OPA743UA	OR2	P6KE6.8AG
OPA694ID	OPA77EZ	OR2	P6KE6.8ARLG
OPA694IDBVR	OPA77FP	OR3	P6KE8.2A-E3/54
OPA698ID	OPA77FZ	OR3	P6KE9.1A-E3/54

Multisim 14.1 Base Edition Components

P6SMB11CAT3G	PBHV8115X	PBLS1502Y	PBLS4004D
P6SMB13AT3G	PBHV8115Z	PBLS1503V	PBLS4004V
P6SMB15AT3G	PBHV8118T	PBLS1503Y	PBLS4004Y
P6SMB18AT3G	PBHV8140Z	PBLS1504V	PBLS4005D
P6SMB20AT3G	PBHV8215Z	PBLS1504Y	PBLS4005V
P6SMB22AT3G	PBHV8540T	PBLS2001D	PBLS4005Y
P6SMB22CAT3G	PBHV8540X	PBLS2001S	PBLS6001D
P6SMB24A-E3/52	PBHV8540Z	PBLS2002D	PBLS6002D
P6SMB24AT3G	PBHV8560Z	PBLS2002S	PBLS6003D
P6SMB24CA-E3/52	PBHV9040T	PBLS2003D	PBLS6004D
P6SMB24CAT3G	PBHV9040X	PBLS2003S	PBLS6005D
P6SMB33A-E3/52	PBHV9040Z	PBLS2004D	PBLS6021D
P6SMB33AT3G	PBHV9050T	PBLS2021D	PBLS6022D
P6SMB36A-E3/52	PBHV9050Z	PBLS2022D	PBLS6023D
P6SMB43CAT3G	PBHV9115T	PBLS2023D	PBLS6024D
P6SMB51CAT3G	PBHV9115X	PBLS2024D	PBRN113ET
P6SMB6.8AT3G	PBHV9115Z	PBLS4001D	PBRN113ZT
P6SMB62AT3G	PBHV9215Z	PBLS4001V	PBRN123ET
P6SMB68AT3G	PBHV9414Z	PBLS4001Y	PBRN123YT
PAR_GEN_CHK	PBHV9515QA	PBLS4002D	PBRP113ET
PB_DPST	PBHV9540Z	PBLS4002V	PBRP113ZT
PB_DPST	PBHV9560Z	PBLS4002Y	PBRP123ET
PB_NC	PBLS1501V	PBLS4003D	PBRP123YT
PB_NO	PBLS1501Y	PBLS4003V	PBSS2515E
PBHV8115T	PBLS1502V	PBLS4003Y	PBSS2515M

Multisim 14.1 Base Edition Components

PBSS2515MB	PBSS304ND	PBSS4021NZ	PBSS4041SP
PBSS2515VPN	PBSS304NX	PBSS4021PT	PBSS4041SPN
PBSS2515VS	PBSS304NZ	PBSS4021PX	PBSS4112PAN
PBSS2515YPN	PBSS304PD	PBSS4021PZ	PBSS4112PANP
PBSS2540E	PBSS304PX	PBSS4021SN	PBSS4120T
PBSS2540M	PBSS304PZ	PBSS4021SP	PBSS4130PAN
PBSS2540MB	PBSS305ND	PBSS4021SPN	PBSS4130PANP
PBSS301ND	PBSS305NX	PBSS4032ND	PBSS4130QA
PBSS301NX	PBSS305NZ	PBSS4032NT	PBSS4130T
PBSS301NZ	PBSS305PD	PBSS4032NX	PBSS4140DPN
PBSS301PD	PBSS305PX	PBSS4032NZ	PBSS4140T
PBSS301PX	PBSS305PZ	PBSS4032PD	PBSS4140U
PBSS301PZ	PBSS306NX	PBSS4032PT	PBSS4140V
PBSS302ND	PBSS306NZ	PBSS4032PX	PBSS4160DPN
PBSS302NX	PBSS306PX	PBSS4032PZ	PBSS4160DS
PBSS302NZ	PBSS306PZ	PBSS4032SN	PBSS4160PAN
PBSS302PD	PBSS3515E	PBSS4032SP	PBSS4160PANP
PBSS302PX	PBSS3515M	PBSS4032SPN	PBSS4160QA
PBSS302PZ	PBSS3515MB	PBSS4041NT	PBSS4160T
PBSS303ND	PBSS3515VS	PBSS4041NX	PBSS4160U
PBSS303NX	PBSS3540E	PBSS4041NZ	PBSS4160V
PBSS303NZ	PBSS3540M	PBSS4041PT	PBSS4220PANS
PBSS303PD	PBSS3540MB	PBSS4041PX	PBSS4220V
PBSS303PX	PBSS4021NT	PBSS4041PZ	PBSS4230PAN
PBSS303PZ	PBSS4021NX	PBSS4041SN	PBSS4230PANP

Multisim 14.1 Base Edition Components

PBSS4230QA	PBSS4440D	PBSS5220T	PBSS5350Z
PBSS4230T	PBSS4480X	PBSS5220V	PBSS5360Z
PBSS4240DPN	PBSS4520X	PBSS5230PAP	PBSS5420D
PBSS4240T	PBSS4540X	PBSS5230QA	PBSS5440D
PBSS4240V	PBSS4540Z	PBSS5230T	PBSS5480X
PBSS4240X	PBSS4560PA	PBSS5240T	PBSS5520X
PBSS4240Y	PBSS4580PA	PBSS5240V	PBSS5540X
PBSS4250X	PBSS4612PA	PBSS5240X	PBSS5540Z
PBSS4260PAN	PBSS4620PA	PBSS5240Y	PBSS5560PA
PBSS4260PANP	PBSS4630PA	PBSS5250T	PBSS5580PA
PBSS4260PANS	PBSS5112PAP	PBSS5250X	PBSS5612PA
PBSS4260QA	PBSS5120T	PBSS5255PAPS	PBSS5620PA
PBSS4320T	PBSS5130PAP	PBSS5260PAP	PBSS5630PA
PBSS4320X	PBSS5130QA	PBSS5260PAPS	PBSS8110D
PBSS4330PA	PBSS5130T	PBSS5260QA	PBSS8110T
PBSS4330PAS	PBSS5140T	PBSS5320D	PBSS8110X
PBSS4330X	PBSS5140U	PBSS5320T	PBSS8110Y
PBSS4350D	PBSS5140V	PBSS5320X	PBSS8110Z
PBSS4350SPN	PBSS5160DS	PBSS5330PA	PBSS8510PA
PBSS4350SS	PBSS5160PAP	PBSS5330PAS	PBSS9110D
PBSS4350T	PBSS5160QA	PBSS5330X	PBSS9110T
PBSS4350X	PBSS5160T	PBSS5350D	PBSS9110X
PBSS4350Z	PBSS5160U	PBSS5350SS	PBSS9110Y
PBSS4360Z	PBSS5160V	PBSS5350T	PBSS9110Z
PBSS4420D	PBSS5220PAPS	PBSS5350X	PBSS9410PA

Multisim 14.1 Base Edition Components

PCP1208-TD-H	PDTA114ET	PDTA123ET	PDTA124TU
PD15-22B/TR8	PDTA114EU	PDTA123EU	PDTA124XE
PD15-22C/TR8	PDTA114TE	PDTA123JE	PDTA124XM
PD70-01B/TR7	PDTA114TM	PDTA123JM	PDTA124XMB
PD93-21C/TR8	PDTA114TMB	PDTA123JMB	PDTA124XT
PD95-21B/TR10	PDTA114TT	PDTA123JT	PDTA124XU
PDB-C134	PDTA114TU	PDTA123JU	PDTA143EE
PDB-C134F	PDTA114YE	PDTA123TM	PDTA143EM
PDB-C139	PDTA114YM	PDTA123TMB	PDTA143EMB
PDB-C142D	PDTA114YMB	PDTA123TT	PDTA143ET
PDB-C152SM	PDTA114YT	PDTA123TU	PDTA143EU
PDB-C156	PDTA114YU	PDTA123YE	PDTA143TE
PDTA113EE	PDTA115EE	PDTA123YM	PDTA143TM
PDTA113EM	PDTA115EM	PDTA123YMB	PDTA143TMB
PDTA113EMB	PDTA115EMB	PDTA123YT	PDTA143TT
PDTA113ET	PDTA115ET	PDTA123YU	PDTA143TU
PDTA113EU	PDTA115EU	PDTA124EE	PDTA143XE
PDTA113ZE	PDTA115TE	PDTA124EM	PDTA143XM
PDTA113ZM	PDTA115TM	PDTA124EMB	PDTA143XMB
PDTA113ZMB	PDTA115TMB	PDTA124ET	PDTA143XT
PDTA113ZT	PDTA115TT	PDTA124EU	PDTA143XU
PDTA113ZU	PDTA115TU	PDTA124TE	PDTA143ZE
PDTA114EE	PDTA123EE	PDTA124TM	PDTA143ZM
PDTA114EM	PDTA123EM	PDTA124TMB	PDTA143ZMB
PDTA114EMB	PDTA123EMB	PDTA124TT	PDTA143ZT

Multisim 14.1 Base Edition Components

PDTA143ZU	PDTB113ZT	PDTC114TMB	PDTC123JMB
PDTA144EE	PDTB113ZU	PDTC114TT	PDTC123JT
PDTA144EM	PDTB114EQA	PDTC114TU	PDTC123JU
PDTA144EMB	PDTB114ET	PDTC114YE	PDTC123TE
PDTA144ET	PDTB114EU	PDTC114YM	PDTC123TM
PDTA144EU	PDTB123EQA	PDTC114YMB	PDTC123TMB
PDTA144TE	PDTB123ET	PDTC114YT	PDTC123TT
PDTA144TM	PDTB123EU	PDTC114YU	PDTC123TU
PDTA144TMB	PDTB123TT	PDTC115EE	PDTC123YE
PDTA144TT	PDTB123YQA	PDTC115EM	PDTC123YM
PDTA144TU	PDTB123YT	PDTC115EMB	PDTC123YMB
PDTA144VE	PDTB123YU	PDTC115ET	PDTC123YT
PDTA144VM	PDTB143EQA	PDTC115EU	PDTC123YU
PDTA144VMB	PDTB143ET	PDTC115TE	PDTC124EE
PDTA144VT	PDTB143EU	PDTC115TM	PDTC124EM
PDTA144VU	PDTB143XQA	PDTC115TMB	PDTC124EMB
PDTA144WE	PDTB143XT	PDTC115TT	PDTC124ET
PDTA144WM	PDTB143XU	PDTC115TU	PDTC124EU
PDTA144WMB	PDTC114EE	PDTC123EE	PDTC124TE
PDTA144WT	PDTC114EM	PDTC123EM	PDTC124TM
PDTA144WU	PDTC114EMB	PDTC123EMB	PDTC124TMB
PDTB113EQA	PDTC114ET	PDTC123ET	PDTC124TT
PDTB113ET	PDTC114EU	PDTC123EU	PDTC124TU
PDTB113EU	PDTC114TE	PDTC123JE	PDTC124XE
PDTB113ZQA	PDTC114TM	PDTC123JM	PDTC124XM

Multisim 14.1 Base Edition Components

PDTC124XMB	PDTC144EMB	PDTD114ET	PDZ24B
PDTC124XT	PDTC144ET	PDTD114EU	PDZ3.0B
PDTC124XU	PDTC144EU	PDTD123EQA	PDZ3.3B
PDTC143EE	PDTC144TE	PDTD123ET	PDZ3.6B
PDTC143EM	PDTC144TM	PDTD123EU	PDZ3.9B
PDTC143EMB	PDTC144TMB	PDTD123TT	PDZ4.3B
PDTC143ET	PDTC144TT	PDTD123YQA	PDZ4.7B
PDTC143EU	PDTC144TU	PDTD123YT	PDZ5.1B
PDTC143TE	PDTC144VE	PDTD123YU	PDZ5.6B
PDTC143TM	PDTC144VM	PDTD143EQA	PDZ6.2B
PDTC143TMB	PDTC144VMB	PDTD143ET	PDZ6.8B
PDTC143TT	PDTC144VT	PDTD143EU	PDZ7.5B
PDTC143TU	PDTC144VU	PDTD143XQA	PDZ9.1B
PDTC143XE	PDTC144WE	PDTD143XT	PEMB1
PDTC143XM	PDTC144WM	PDTD143XU	PEMB10
PDTC143XMB	PDTC144WMB	PDZ10B	PEMB11
PDTC143XT	PDTC144WT	PDZ11B	PEMB13
PDTC143XU	PDTC144WU	PDZ12B	PEMB14
PDTC143ZE	PDTD113EQA	PDZ13B	PEMB15
PDTC143ZM	PDTD113ET	PDZ15B	PEMB16
PDTC143ZMB	PDTD113EU	PDZ16B	PEMB17
PDTC143ZT	PDTD113ZQA	PDZ18B	PEMB18
PDTC143ZU	PDTD113ZT	PDZ2.7B	PEMB19
PDTC144EE	PDTD113ZU	PDZ20B	PEMB2
PDTC144EM	PDTD114EQA	PDZ22B	PEMB20

Multisim 14.1 Base Edition Components

PEMB24	PEMH10	PESD12VS1UL	PESD24VL2BT
PEMB3	PEMH11	PESD12VS1ULD	PESD24VS1UA
PEMB30	PEMH13	PESD12VS2UAT	PESD24VS1UB
PEMB4	PEMH14	PESD12VS2UQ	PESD24VS1UL
PEMB9	PEMH15	PESD12VS2UT	PESD24VS1ULD
PEMD10	PEMH16	PESD12VS4UD	PESD24VS2UAT
PEMD12	PEMH17	PESD12VS5UD	PESD24VS2UQ
PEMD13	PEMH18	PESD12VU1UT	PESD24VS2UT
PEMD14	PEMH19	PESD12VV1BL	PESD24VS4UD
PEMD15	PEMH2	PESD15VL1BA	PESD24VS5UD
PEMD16	PEMH20	PESD15VL2BT	PESD24VU1UT
PEMD17	PEMH24	PESD15VS1UB	PESD2CAN
PEMD18	PEMH30	PESD15VS1UL	PESD36VS1UL
PEMD19	PEMH4	PESD15VS1ULD	PESD36VS2UT
PEMD2	PEMH7	PESD15VS2UAT	PESD3V3L1BA
PEMD20	PEMH9	PESD15VS2UQ	PESD3V3L1UA
PEMD24	PEMT1	PESD15VS2UT	PESD3V3L1UB
PEMD3	PEMX1	PESD15VS4UD	PESD3V3L1UL
PEMD30	PEMZ1	PESD15VS5UD	PESD3V3L2BT
PEMD4	PEMZ7	PESD15VU1UT	PESD3V3L2UM
PEMD48	PESD12VL1BA	PESD16VX1UL	PESD3V3L4UF
PEMD6	PESD12VL2BT	PESD1CAN	PESD3V3L4UG
PEMD9	PESD12VS1UA	PESD1FLEX	PESD3V3L4UW
PEMF21	PESD12VS1UB	PESD1LIN	PESD3V3L5UF
PEMH1	PESD12VS1UJ	PESD24VL1BA	PESD3V3L5UK

Multisim 14.1 Base Edition Components

PESD3V3L5UV	PESD5V0L2UM	PESD5V0S5UD	PESD5V0X1UB
PESD3V3L5UY	PESD5V0L4UF	PESD5V0U1BA	PESD5V0X1ULD
PESD3V3S1UB	PESD5V0L4UG	PESD5V0U1BB	PESD5V2S2UT
PESD3V3S1UL	PESD5V0L4UW	PESD5V0U1BL	PESD9V0V4UK
PESD3V3S2UAT	PESD5V0L5UK	PESD5V0U1BLD	PESD9X5.0L
PESD3V3S2UQ	PESD5V0L5UV	PESD5V0U1UA	PESD9X7.0L
PESD3V3S2UT	PESD5V0L5UY	PESD5V0U1UB	PG_13
PESD3V3S4UD	PESD5V0L6UAS	PESD5V0U1UL	PG_9_O_E
PESD3V3S4UF	PESD5V0L6US	PESD5V0U1UT	PHILIPS-MIPS-HDR
PESD3V3S5UD	PESD5V0L7BAS	PESD5V0U2BT	PHN110
PESD3V3U1UT	PESD5V0L7BS	PESD5V0V1BA	PhonePlug
PESD3V3V4UF	PESD5V0S1BA	PESD5V0V1BB	PhonePlug2
PESD3V3V4UG	PESD5V0S1BB	PESD5V0V1BL	PHOTODIODE
PESD3V3V4UK	PESD5V0S1BL	PESD5V0V1BLD	PHOTOTRANSISTOR
PESD3V3V4UW	PESD5V0S1BLD	PESD5V0V4UF	PHP125
PESD5V0F1BL	PESD5V0S1UA	PESD5V0V4UG	PHP225
PESD5V0F1BLD	PESD5V0S1UB	PESD5V0V4UK	PHPT60406NY
PESD5V0F5UF	PESD5V0S1UJ	PESD5V0V4UW	PHPT60406PY
PESD5V0F5UV	PESD5V0S1UL	PESD5V0X1BCAL	PHPT60410NY
PESD5V0L1BA	PESD5V0S1ULD	PESD5V0X1BCL	PHPT60410PY
PESD5V0L1UA	PESD5V0S2BT	PESD5V0X1BL	PHPT60415NY
PESD5V0L1UB	PESD5V0S2UAT	PESD5V0X1BQ	PHPT60415PY
PESD5V0L1UL	PESD5V0S2UQ	PESD5V0X1BT	PHPT60603NY
PESD5V0L1ULD	PESD5V0S4UD	PESD5V0X1UAB	PHPT60603PY
PESD5V0L2BT	PESD5V0S4UF	PESD5V0X1UALD	PHPT60606NY

Multisim 14.1 Base Edition Components

PHPT60606PY	PIC16C54A	PIMD2	PMBD6050
PHPT60610NY	PIC16C54C	PIMD3	PMBD6100
PHPT60610PY	PIC16C554	PIMH9	PMBD7000
PHPT61002NYC	PIC16C558	PIMN31	PMBD7100
PHPT61002PYC	PIC16C56	PIMT1	PMBD914
PHPT61003NY	PIC16C56A	PIMZ2	PMBF170
PHPT61003PY	PIC16C58B	PJ-002B-SMT	PMBF4391
PHPT61006NY	PIC16CR54A	PJ-007	PMBF4392
PHPT61006PY	PIC16CR54C	PJ1-023	PMBF4393
PHPT61010NY	PIC16CR56A	PJ-102A	PMBF4416
PHPT61010PY	PIC16CR58B	PLD-JTAG-HDR	PMBF4416A
PHT4NQ10LT	PIC16CR83	PLL_VIRTUAL	PMBF5484
PHT6N06LT	PIC16CR84	PLUS_MINUS_ONE	PMBF5485
PHT6N06T	PIC16F83	PLUS_MINUS_ONE_	PMBF5486
PHT6NQ10T	PIC18F6620-	BLUE	PMBFJ108
PHT8N06LT	TQFP(64L)	PLUS_MINUS_ONE_	PMBFJ109
PIC12C508	PIC18F6720-	GREEN	PMBFJ110
PIC12C508A	TQFP(64L)	PLUS_MINUS_ONE_	PMBFJ111
PIC12C509	PIC18F8620-	ORANGE	PMBFJ112
PIC12C509A	TQFP(80L)	PLUS_MINUS_ONE_	PMBFJ113
PIC12CE518	PIC18F8720-	YELLOW	PMBFJ114
PIC12CE519	TQFP(80L)	PLVA2656A	PMBFJ174
PIC12CR509A	PIECEWISE_LINEAR	PLVA650A	PMBFJ175
PIC16C505	_CURRENT	PLVA662A	PMBFJ176
PIC16C54	PIECEWISE_LINEAR	PMBD353	PMBFJ177
	_VOLTAGE	PMBD354	PMBFJ210
	PIMC31		

Multisim 14.1 Base Edition Components

PMBFJ211	PMBT3946YPN	PMBZ5232B	PMBZ5257B
PMBFJ212	PMBT4401	PMBZ5233B	PMCM440VNE
PMBFJ308	PMBT4401YS	PMBZ5234B	PMCM650VNE
PMBFJ309	PMBT4403	PMBZ5235B	PMDPB28UN
PMBFJ310	PMBT4403YS	PMBZ5236B	PMDPB30XN
PMBS3904	PMBT5550	PMBZ5237B	PMDPB38UNE
PMBS3906	PMBT5551	PMBZ5238B	PMDPB42UN
PMBT2222	PMBT6428	PMBZ5239B	PMDPB55XP
PMBT2222A	PMBT6429	PMBZ5240B	PMDPB56XN
PMBT2222AYS	PMBTA06	PMBZ5241B	PMDPB56XNEA
PMBT2369	PMBTA13	PMBZ5242B	PMDPB58UPE
PMBT2907	PMBTA14	PMBZ5243B	PMDPB65UP
PMBT2907A	PMBTA42	PMBZ5244B	PMDPB70EN
PMBT2907AYS	PMBTA42DS	PMBZ5245B	PMDPB70XP
PMBT3904	PMBTA44	PMBZ5246B	PMDPB70XPE
PMBT3904M	PMBTA45	PMBZ5247B	PMDPB85UPE
PMBT3904MB	PMBTA56	PMBZ5248B	PMDPB95XNE
PMBT3904VS	PMBTA64	PMBZ5249B	PMDPB95XNE2
PMBT3904YS	PMBTA92	PMBZ5250B	PMDT290UNE
PMBT3906	PMBZ5226B	PMBZ5251B	PMDT670UPE
PMBT3906M	PMBZ5227B	PMBZ5252B	PMDXB1200UPE
PMBT3906MB	PMBZ5228B	PMBZ5253B	PMDXB550UNE
PMBT3906VS	PMBZ5229B	PMBZ5254B	PMDXB600UNE
PMBT3906YS	PMBZ5230B	PMBZ5255B	PMEG045T150EPD
PMBT3946VPN	PMBZ5231B	PMBZ5256B	PMEG045V050EPD

Multisim 14.1 Base Edition Components

PMEG045V100EPD	PMEG2005CT	PMEG2010EV	PMEG3005EB
PMEG045V150EPD	PMEG2005EB	PMEG2015EA	PMEG3005EH
PMEG050T150EPD	PMEG2005EH	PMEG2015EH	PMEG3005EJ
PMEG050V150EPD	PMEG2005EJ	PMEG2015EJ	PMEG3005EL
PMEG060V050EPD	PMEG2005EL	PMEG2015EPK	PMEG3005ELD
PMEG060V100EPD	PMEG2005ELD	PMEG2015EV	PMEG3005ESF
PMEG10020AELR	PMEG2005EPK	PMEG2020AEA	PMEG3005ET
PMEG100V060ELPD	PMEG2005ESF	PMEG2020CPA	PMEG3010AESA
PMEG100V080ELPD	PMEG2005ET	PMEG2020CPAS	PMEG3010AESB
PMEG100V100ELPD	PMEG2010AEB	PMEG2020EH	PMEG3010BEA
PMEG1020EA	PMEG2010AEH	PMEG2020EJ	PMEG3010BEP
PMEG1020EH	PMEG2010AEJ	PMEG2020EPA	PMEG3010BER
PMEG1020EJ	PMEG2010AET	PMEG2020EPAS	PMEG3010BEV
PMEG1020EV	PMEG2010BEA	PMEG2020EPK	PMEG3010CEH
PMEG1030EH	PMEG2010BELD	PMEG3002AEB	PMEG3010CEJ
PMEG1030EJ	PMEG2010BER	PMEG3002AEL	PMEG3010EB
PMEG1201AESF	PMEG2010BEV	PMEG3002AELD	PMEG3010EH
PMEG2002AESF	PMEG2010EA	PMEG3002AESF	PMEG3010EJ
PMEG2002ESF	PMEG2010EH	PMEG3002EJ	PMEG3010EP
PMEG2005AEA	PMEG2010EJ	PMEG3002ESF	PMEG3010ER
PMEG2005AEL	PMEG2010EPA	PMEG3002TV	PMEG3010ET
PMEG2005AELD	PMEG2010EPAS	PMEG3005AEA	PMEG3015EH
PMEG2005AESF	PMEG2010EPK	PMEG3005AESF	PMEG3015EJ
PMEG2005AEV	PMEG2010ER	PMEG3005AEV	PMEG3015EV
PMEG2005BELD	PMEG2010ET	PMEG3005CT	PMEG3020BEP

Multisim 14.1 Base Edition Components

PMEG3020BER	PMEG4005CT	PMEG4020EPK	PMEG6020EPA
PMEG3020CEP	PMEG4005EH	PMEG4020ER	PMEG6020EPAS
PMEG3020CPA	PMEG4005EJ	PMEG4020ETP	PMEG6020ER
PMEG3020CPAS	PMEG4005EPK	PMEG4020ETR	PMEG6020ETP
PMEG3020DEP	PMEG4005ESF	PMEG4030EP	PMEG6020ETR
PMEG3020EH	PMEG4005ET	PMEG4030ER	PMEG6030EP
PMEG3020EJ	PMEG4010AESB	PMEG4030ETP	PMEG6030ETP
PMEG3020EP	PMEG4010BEA	PMEG4050EP	PMF170XP
PMEG3020EPA	PMEG4010BEV	PMEG4050ETP	PMF250XN
PMEG3020EPAS	PMEG4010CEH	PMEG45A10EPD	PMF250XNE
PMEG3020ER	PMEG4010CEJ	PMEG45U10EPD	PMF280UN
PMEG3030BEP	PMEG4010CPA	PMEG6002EB	PMF290XN
PMEG3030EP	PMEG4010CPAS	PMEG6002EJ	PMF3800SN
PMEG3050BEP	PMEG4010EH	PMEG6002TV	PMF400UN
PMEG3050EP	PMEG4010EJ	PMEG6010AED	PMF63UN
PMEG4002AESF	PMEG4010EP	PMEG6010CEH	PMF63UNE
PMEG4002EB	PMEG4010EPK	PMEG6010CEJ	PMF77XN
PMEG4002EJ	PMEG4010ER	PMEG6010CPA	PMF780SN
PMEG4002EL	PMEG4010ET	PMEG6010CPAS	PMF87EN
PMEG4002ELD	PMEG4010ETP	PMEG6010ELR	PMFPB6532UP
PMEG4002ESF	PMEG4010ETR	PMEG6010EP	PMFPB6545UP
PMEG4005AEA	PMEG4015EPK	PMEG6010ER	PMG370XN
PMEG4005AESF	PMEG4020EP	PMEG6010ETR	PMG45UN
PMEG4005AEV	PMEG4020EPA	PMEG6020ELR	PMG85XP
PMEG4005CEJ	PMEG4020EPAS	PMEG6020EP	PMGD130UN

Multisim 14.1 Base Edition Components

PMGD175XN	PMLL5240B	PMLL5265B	PMN50UPE
PMGD175XNE	PMLL5241B	PMLL5266B	PMN52XP
PMGD280UN	PMLL5242B	PMMT491A	PMN70XP
PMGD290XN	PMLL5243B	PMMT591A	PMN70XPE
PMGD370XN	PMLL5244B	PMN16XNE	PMN70XPEA
PMGD400UN	PMLL5245B	PMN20EN	PMN80XP
PMGD780SN	PMLL5246B	PMN22XN	PMP4201G
PMGD8000LN	PMLL5247B	PMN25EN	PMP4201V
PMLL4148L	PMLL5248B	PMN25UN	PMP4201Y
PMLL4448	PMLL5249B	PMN27UP	PMP4501G
PMLL5225B	PMLL5250B	PMN27XPE	PMP4501V
PMLL5226B	PMLL5251B	PMN27XPEA	PMP4501Y
PMLL5227B	PMLL5252B	PMN28UN	PMP5201G
PMLL5228B	PMLL5253B	PMN30UN	PMP5201V
PMLL5229B	PMLL5254B	PMN30UNE	PMP5201Y
PMLL5230B	PMLL5255B	PMN30XP	PMP5501G
PMLL5231B	PMLL5256B	PMN34UN	PMP5501V
PMLL5232B	PMLL5257B	PMN34UP	PMP5501Y
PMLL5233B	PMLL5258B	PMN35EN	PMPB10XNE
PMLL5234B	PMLL5259B	PMN40LN	PMPB11EN
PMLL5235B	PMLL5260B	PMN40UPE	PMPB12UN
PMLL5236B	PMLL5261B	PMN40UPEA	PMPB12UNE
PMLL5237B	PMLL5262B	PMN42XPE	PMPB13XNE
PMLL5238B	PMLL5263B	PMN42XPEA	PMPB15XN
PMLL5239B	PMLL5264B	PMN48XP	PMPB15XP

Multisim 14.1 Base Edition Components

PMPB16XN	PMSS3906	PMV100ENEA	PMV30XPEA
PMPB19XP	PMST2222	PMV117EN	PMV31XN
PMPB20EN	PMST2222A	PMV120ENEA	PMV32UP
PMPB20UN	PMST2369	PMV130ENEA	PMV33UPE
PMPB20XNEA	PMST2907A	PMV160UP	PMV37EN
PMPB20XPE	PMST3904	PMV16UN	PMV37EN2
PMPB215ENEA	PMST3906	PMV16XN	PMV40UN
PMPB23XNE	PMST4401	PMV170UN	PMV40UN2
PMPB27EP	PMST4403	PMV185XN	PMV42ENE
PMPB29XNE	PMST5088	PMV20EN	PMV45EN
PMPB29XPE	PMST5089	PMV20XN	PMV45EN2
PMPB33XN	PMST5550	PMV20XNE	PMV48XP
PMPB33XP	PMST5551	PMV20XNEA	PMV50ENEA
PMPB43XPE	PMST6428	PMV213SN	PMV50UPE
PMPB47XP	PMST6429	PMV22EN	PMV50XP
PMPB85ENEA	PMSTA05	PMV230ENEA	PMV55ENEA
PMPB95ENEA	PMSTA06	PMV250EPEA	PMV60EN
PMR280UN	PMSTA42	PMV25ENEA	PMV65ENEA
PMR290UNE	PMSTA55	PMV27UPE	PMV65UN
PMR290XN	PMSTA56	PMV27UPEA	PMV65UNE
PMR370XN	PMSTA92	PMV28UN	PMV65XP
PMR400UN	PMT200EN	PMV28UNEA	PMV65XPE
PMR670UPE	PMT21EN	PMV30UN	PMV65XPEA
PMR780SN	PMT29EN	PMV30UN2	PMV75UP
PMSS3904	PMT760EN	PMV30XN	PMV90EN

Multisim 14.1 Base Edition Components

PMXB120EPE	PMZB290UN	PN3641	PN4416
PMXB350UPE	PMZB290UNE2	PN3642	PN4416A
PMXB360ENEA	PMZB300XN	PN3643	PN4916
PMXB40UNE	PMZB320UPE	PN3644	PN4917
PMXB43UNE	PMZB350UPE	PN3645	PN5128
PMXB56EN	PMZB370UNE	PN3646	PN5129
PMXB65ENE	PMZB380XN	PN3694	PN5133
PMXB65UPE	PMZB390UNE	PN4121	PN5134
PMXB75UPE	PMZB420UN	PN4122	PN5135
PMZ1000UN	PMZB550UNE	PN4141	PN5136
PMZ1200UPE	PMZB670UPE	PN4143	PN5137
PMZ130UNE	PMZB790SN	PN4248	PN5138
PMZ200UNE	PN2222	PN4249	PN5139
PMZ250UN	PN2222A	PN4250	PN5142
PMZ270XN	PN2369	PN4250A	PN5179
PMZ290UNE	PN2369A	PN4258	PN5910
PMZ290UNE2	PN2484	PN4258A	PN930
PMZ320UPE	PN2906	PN4274	PNS40010ER
PMZ350XN	PN2906A	PN4275	POLYNOMIAL_VOLT AGE
PMZ390UN	PN2907	PN4354	POTENTIOMETER
PMZ390UNE	PN2907A	PN4355	POTENTIOMETER_V IRTUAL
PMZ550UNE	PN3565	PN4356	
PMZ760SN	PN3638	PN4391	PQMB11
PMZB1200UPE	PN3638A	PN4392	PQMD10
PMZB200UNE	PN3640	PN4393	PQMD12

Multisim 14.1 Base Edition Components

PQMD13	PTVS10VP1UTP	PTVS16VS1UR	PTVS26VS1UTR
PQMD16	PTVS10VS1UR	PTVS16VS1UTR	PTVS28VP1UP
PQMD2	PTVS10VS1UTR	PTVS17VP1UP	PTVS28VP1UTP
PQMD3	PTVS11VP1UP	PTVS17VP1UTP	PTVS28VS1UR
PQMH10	PTVS11VP1UTP	PTVS17VS1UR	PTVS28VS1UTR
PQMH11	PTVS11VS1UR	PTVS17VS1UTR	PTVS30VP1UP
PQMH13	PTVS11VS1UTR	PTVS18VP1UP	PTVS30VP1UTP
PQMH2	PTVS12VP1UP	PTVS18VP1UTP	PTVS30VS1UR
PQMH9	PTVS12VP1UTP	PTVS18VS1UR	PTVS30VS1UTR
PROBE	PTVS12VS1UR	PTVS18VS1UTR	PTVS33VP1UP
PROBE_BLUE	PTVS12VS1UTR	PTVS20VP1UP	PTVS33VP1UTP
PROBE_DIG	PTVS13VP1UP	PTVS20VP1UTP	PTVS33VS1UR
PROBE_DIG_BLUE	PTVS13VP1UTP	PTVS20VS1UR	PTVS33VS1UTR
PROBE_DIG_GREEN	PTVS13VS1UR	PTVS20VS1UTR	PTVS36VP1UP
PROBE_DIG_ORANGE	PTVS13VS1UTR	PTVS22VP1UP	PTVS36VP1UTP
PROBE_DIG_RED	PTVS14VP1UP	PTVS22VP1UTP	PTVS36VS1UR
PROBE_DIG_YELLOW	PTVS14VP1UTP	PTVS22VS1UR	PTVS36VS1UTR
PROBE_GREEN	PTVS14VS1UR	PTVS22VS1UTR	PTVS3V3P1UP
PROBE_ORANGE	PTVS14VS1UTR	PTVS24VP1UP	PTVS3V3P1UTP
PROBE_RED	PTVS15VP1UP	PTVS24VP1UTP	PTVS3V3S1UR
PROBE_YELLOW	PTVS15VP1UTP	PTVS24VS1UR	PTVS3V3S1UTR
PRTR5V0U1T	PTVS15VS1UR	PTVS24VS1UTR	PTVS40VP1UP
PRTR5V0U2X	PTVS15VS1UTR	PTVS26VP1UP	PTVS40VP1UTP
PTVS10VP1UP	PTVS16VP1UP	PTVS26VP1UTP	PTVS40VS1UR
	PTVS16VP1UTP	PTVS26VS1UR	PTVS40VS1UTR

Multisim 14.1 Base Edition Components

PTVS43VP1UP	PTVS5V0P1UTP	PTVS8V0P1UP	PUMB20
PTVS43VP1UTP	PTVS5V0S1UR	PTVS8V0P1UTP	PUMB24
PTVS43VS1UR	PTVS5V0S1UTR	PTVS8V0S1UR	PUMB3
PTVS43VS1UTR	PTVS60VP1UP	PTVS8V0S1UTR	PUMB30
PTVS45VP1UP	PTVS60VP1UTP	PTVS8V5P1UP	PUMB4
PTVS45VP1UTP	PTVS60VS1UR	PTVS8V5P1UTP	PUMB9
PTVS45VS1UR	PTVS60VS1UTR	PTVS8V5S1UR	PUMD10
PTVS45VS1UTR	PTVS64VP1UP	PTVS8V5S1UTR	PUMD12
PTVS48VP1UP	PTVS64VP1UTP	PTVS9V0P1UP	PUMD13
PTVS48VP1UTP	PTVS6V0P1UP	PTVS9V0P1UTP	PUMD14
PTVS48VS1UR	PTVS6V0P1UTP	PTVS9V0S1UR	PUMD15
PTVS48VS1UTR	PTVS6V0S1UR	PTVS9V0S1UTR	PUMD16
PTVS51VP1UP	PTVS6V0S1UTR	PULSE_CURRENT	PUMD17
PTVS51VP1UTP	PTVS6V5P1UP	PULSE_VOLTAGE	PUMD18
PTVS51VS1UR	PTVS6V5P1UTP	PUMB1	PUMD19
PTVS51VS1UTR	PTVS6V5S1UR	PUMB10	PUMD2
PTVS54VP1UP	PTVS6V5S1UTR	PUMB11	PUMD20
PTVS54VP1UTP	PTVS7V0P1UP	PUMB13	PUMD24
PTVS54VS1UR	PTVS7V0P1UTP	PUMB14	PUMD3
PTVS54VS1UTR	PTVS7V0S1UR	PUMB15	PUMD30
PTVS58VP1UP	PTVS7V0S1UTR	PUMB16	PUMD4
PTVS58VP1UTP	PTVS7V5P1UP	PUMB17	PUMD48
PTVS58VS1UR	PTVS7V5P1UTP	PUMB18	PUMD6
PTVS58VS1UTR	PTVS7V5S1UR	PUMB19	PUMD9
PTVS5V0P1UP	PTVS7V5S1UTR	PUMB2	PUMH1

Multisim 14.1 Base Edition Components

PUMH10	PXT2907A	PZTA44	PZU12B
PUMH11	PXT4401	PZTA92	PZU12B1
PUMH13	PXT4403	PZTA92T1G	PZU12B1A
PUMH14	PXTA14	PZU10B	PZU12B2
PUMH15	PXTA42	PZU10B1	PZU12B2A
PUMH16	PXTA92	PZU10B1A	PZU12B2L
PUMH17	PZFI108	PZU10B2	PZU12B3
PUMH18	PZFI109	PZU10B2A	PZU12B3A
PUMH19	PZFI110	PZU10B2L	PZU12BA
PUMH2	PZT2222A	PZU10B3	PZU12BL
PUMH20	PZT2222AT1G	PZU10B3A	PZU12DB2
PUMH24	PZT2907A	PZU10BA	PZU13B
PUMH30	PZT2907AT1	PZU10BL	PZU13B1
PUMH4	PZT2907AT1G	PZU10DB2	PZU13B1A
PUMH7	PZT2907AT3G	PZU11B	PZU13B2
PUMH9	PZT4401	PZU11B1	PZU13B2A
PUMT1	PZT4403	PZU11B1A	PZU13B2L
PUMX1	PZT651T1	PZU11B2	PZU13B3
PUMX2	PZT651T1G	PZU11B2A	PZU13B3A
PUMZ1	PZT751T1	PZU11B2L	PZU13BA
PUMZ2	PZT751T1G	PZU11B3	PZU13BL
PUSH_BUTTON_DP ST	PZTA14	PZU11B3A	PZU13DB2
	PZTA42	PZU11BA	PZU14B2
PWM	PZTA42T1	PZU11BL	PZU14B2A
PXT2222A	PZTA42T1G	PZU11DB2	PZU14B2L

Multisim 14.1 Base Edition Components

PZU14DB2	PZU18B1A	PZU20B2A	PZU24B3A
PZU15B	PZU18B2	PZU20B2L	PZU24BA
PZU15B1	PZU18B2A	PZU20B3	PZU24BL
PZU15B1A	PZU18B2L	PZU20B3A	PZU24DB2
PZU15B2	PZU18B3	PZU20BA	PZU27B
PZU15B2A	PZU18B3A	PZU20BL	PZU27BA
PZU15B2L	PZU18BA	PZU20DB2	PZU27BL
PZU15B3	PZU18BL	PZU22B	PZU3.0B
PZU15B3A	PZU18DB2	PZU22B1	PZU3.0B1
PZU15BA	PZU2.4B	PZU22B1A	PZU3.0B1A
PZU15BL	PZU2.4BA	PZU22B2	PZU3.0B2
PZU15DB2	PZU2.4BL	PZU22B2A	PZU3.0B2A
PZU16B	PZU2.7B	PZU22B2L	PZU3.0B2L
PZU16B1	PZU2.7B1	PZU22B3	PZU3.0BA
PZU16B1A	PZU2.7B1A	PZU22B3A	PZU3.0BL
PZU16B2	PZU2.7B2	PZU22BA	PZU3.0DB2
PZU16B2A	PZU2.7B2A	PZU22BL	PZU3.3B
PZU16B2L	PZU2.7B2L	PZU22DB2	PZU3.3B1
PZU16B3	PZU2.7BA	PZU24B	PZU3.3B1A
PZU16B3A	PZU2.7BL	PZU24B1	PZU3.3B2
PZU16BA	PZU2.7DB2	PZU24B1A	PZU3.3B2A
PZU16BL	PZU20B	PZU24B2	PZU3.3B2L
PZU16DB2	PZU20B1	PZU24B2A	PZU3.3BA
PZU18B	PZU20B1A	PZU24B2L	PZU3.3BL
PZU18B1	PZU20B2	PZU24B3	PZU3.3DB2

Multisim 14.1 Base Edition Components

PZU3.6B	PZU36BA	PZU5.1B1	PZU6.2B2A
PZU3.6B1	PZU36BL	PZU5.1B1A	PZU6.2B2L
PZU3.6B1A	PZU4.3B	PZU5.1B2	PZU6.2B3
PZU3.6B2	PZU4.3B1	PZU5.1B2A	PZU6.2B3A
PZU3.6B2A	PZU4.3B1A	PZU5.1B2L	PZU6.2BA
PZU3.6B2L	PZU4.3B2	PZU5.1B3	PZU6.2BL
PZU3.6BA	PZU4.3B2A	PZU5.1B3A	PZU6.2DB2
PZU3.6BL	PZU4.3B2L	PZU5.1BA	PZU6.8B
PZU3.6DB2	PZU4.3B3	PZU5.1BL	PZU6.8B1
PZU3.9B	PZU4.3B3A	PZU5.1DB2	PZU6.8B1A
PZU3.9B1	PZU4.3BA	PZU5.6B	PZU6.8B2
PZU3.9B1A	PZU4.3BL	PZU5.6B1	PZU6.8B2A
PZU3.9B2	PZU4.3DB2	PZU5.6B1A	PZU6.8B2L
PZU3.9B2A	PZU4.7B	PZU5.6B2	PZU6.8B3
PZU3.9B2L	PZU4.7B1	PZU5.6B2A	PZU6.8B3A
PZU3.9BA	PZU4.7B1A	PZU5.6B2L	PZU6.8BA
PZU3.9BL	PZU4.7B2	PZU5.6B3	PZU6.8BL
PZU3.9DB2	PZU4.7B2A	PZU5.6B3A	PZU6.8DB2
PZU30B	PZU4.7B2L	PZU5.6BA	PZU7.5B
PZU30BA	PZU4.7B3	PZU5.6BL	PZU7.5B1
PZU30BL	PZU4.7B3A	PZU5.6DB2	PZU7.5B1A
PZU33B	PZU4.7BA	PZU6.2B	PZU7.5B2
PZU33BA	PZU4.7BL	PZU6.2B1	PZU7.5B2A
PZU33BL	PZU4.7DB2	PZU6.2B1A	PZU7.5B2L
PZU36B	PZU5.1B	PZU6.2B2	PZU7.5B3

Multisim 14.1 Base Edition Components

PZU7.5B3A	PZU9.1DB2	RC4558P	REF01AJ
PZU7.5BA	QL6250-4PQ208C	RC4558Y	REF01AJ/883C
PZU7.5BL	QUAD_MUX_2TO1	RC4559D	REF01CJ
PZU7.5DB2	QUAD_REG	RC4559P	REF01CP
PZU8.2B	R145-32.768kHz	RCJ-011-SMT	REF01CPZ
PZU8.2B1	R26-32.768kHz	RCJ-32234	REF01CS
PZU8.2B1A	R38-32.768kHz	RD10	REF01EZ
PZU8.2B2	R710XPT	RD11	REF01HPZ
PZU8.2B2A	R711XPT	RD12	REF01HS
PZU8.2B2L	R712XPT	RD15	REF01HZ
PZU8.2B3	R714XPT	RD15SB	REF02AJ
PZU8.2B3A	RB520CS3002L	RD2.0S	REF02AJ/883C
PZU8.2BA	RB520CS30L	RD2.2S	REF02AZ
PZU8.2BL	RB520S30	RD2.4S	REF02CP
PZU8.2DB2	RB521CS30L	RD2.7S	REF02CS
PZU9.1B	RB521S30	RD3.0S	REF02CZ
PZU9.1B1	RB521S30T1G	RD4.7	REF02EZ
PZU9.1B1A	RB521S30T5G	RD5.1	REF02HPZ
PZU9.1B2	RB751CS40	RD5.6	REF02HSZ
PZU9.1B2A	RB751S40	RD6.2	REF02HZ
PZU9.1B2L	RB751S40T1G	RD6.8	REF02RC
PZU9.1B3	RB751V40	RD7.5	REF02RC/883C
PZU9.1B3A	RC4136D	RD7.5SB	REF191ES
PZU9.1BA	RC4136N	RD8.2	REF191GP
PZU9.1BL	RC4558D	RD9.2	REF191GS

Multisim 14.1 Base Edition Components

REF192ES	REF198GP	REF3330AIDCKR	REF5040AIDGKR
REF192FS	REF198GRU	REF3333AIDBZR	REF5040AIDR
REF192GP	REF198GRUZ	REF3333AIDCKR	REF5040ID
REF192GPZ	REF198GS	REF43FZ	REF5040IDGKR
REF192GRU	REF3012_SOT23_3	REF43GP	REF5040IDR
REF192GRUZ	REF3020_SOT23_3	REF43GPZ	REF5045AID
REF192GS	REF3025_SOT23_3	REF43GS	REF5045AIDGKR
REF193GS	REF3033_SOT23_3	REF5010AID	REF5045AIDR
REF193GSZ	REF3040_SOT23_3	REF5010AIDGKR	REF5045ID
REF194ES	REF3120AIDBZR	REF5010ID	REF5045IDGKR
REF194GP	REF3212AIDBVR	REF5010IDGKR	REF5045IDR
REF194GSZ	REF3220AIDBVR	REF5020AID	REF5050AID
REF195ES	REF3225AIDBVR	REF5020AIDGKR	REF5050AIDGKR
REF195FS	REF3230AIDBVR	REF5020ID	REF5050AIDR
REF195GP	REF3233AIDBVR	REF5020IDGKR	REF5050ID
REF195GPZ	REF3240AIDBVR	REF5025AID	REF5050IDGKR
REF195GRU	REF3312AIDBZR	REF5025AIDGKR	REF5050IDR
REF195GRUZ	REF3312AIDCKR	REF5025ID	REG_FILE_2Px4
REF195GS	REF3318AIDBZR	REF5025IDGKR	REG_FILE_4x4
REF196GRU	REF3318AIDCKR	REF5030AID	RELAY_NC
REF196GRU-REEL7	REF3320AIDBZR	REF5030AIDGKR	RELAY_NO
REF196GS	REF3320AIDCKR	REF5030ID	RELAY_NONC
REF196GSZ	REF3325AIDBZR	REF5030IDGKR	RELAY1A_VIRTUAL
REF198ES	REF3325AIDCKR	REF5030IDR	RELAY1B_VIRTUAL
REF198FSZ	REF3330AIDBZR	REF5040AID	RELAY1C_VIRTUAL

Multisim 14.1 Base Edition Components

RESISTOR_VIRTUAL	RGP10D	RGP30A	RIBBON_16H_MNT
REVERSE_1A	RGP10G	RGP30B	RIBBON_16V
REVERSE_2A	RGP10J	RGP30D	RIBBON_16V_LATC H
REVERSE_3A	RGP10K	RGP30G	RIBBON_16V_MNT
REVERSE_4A	RGP10M	RGP30J	RIBBON_20H
RGF1A	RGP10M-E3/54	RGP30K	RIBBON_20H_LATC H
RGF1B	RGP15A	RGP30M	RIBBON_20H_MNT
RGF1D	RGP15B	R-HI-008068-2	RIBBON_20V
RGF1G	RGP15D	RIBBON_10H	RIBBON_20V_LATC H
RGF1J	RGP15G	RIBBON_10H_LATC H	RIBBON_20V_MNT
RGF1K	RGP15J	RIBBON_10H_MNT	RIBBON_24H
RGF1M	RGP15K	RIBBON_10V	RIBBON_24H_LATC H
RGL34A	RGP15M	RIBBON_10V_LATC H	RIBBON_24H_MNT
RGL34B	RGP20A	RIBBON_10V_MNT	RIBBON_24V
RGL34D	RGP20B	RIBBON_14H	RIBBON_24V_LATC H
RGL34G	RGP20D	RIBBON_14H_LATC H	RIBBON_24V_MNT
RGL34J	RGP20G	RIBBON_14H_MNT	RIBBON_26H
RGP02-12E	RGP20J	RIBBON_14V	RIBBON_26H_LATC H
RGP02-14E	RGP25A	RIBBON_14V_LATC H	RIBBON_26H_MNT
RGP02-16E	RGP25B	RIBBON_14V_MNT	RIBBON_26V
RGP02-18E	RGP25D	RIBBON_16H	RIBBON_26V_LATC H
RGP02-20E	RGP25G	RIBBON_16H_LATC H	
RGP02-20E-E3/54	RGP25J		
RGP10A	RGP25K		
RGP10B	RGP25M		

Multisim 14.1 Base Edition Components

RIBBON_26V_MNT	RIBBON_50H_MNT	S1227-33BR	SA5.0A-E3/54
RIBBON_30H	RIBBON_50V	S1227-66BQ	SA5.0CA-E3/54
RIBBON_30H_LATC H	RIBBON_50V_LATC H	S1227-66BR	SA6.0A-E3/54
RIBBON_30H_MNT	RIBBON_50V_MNT	S1B-E3/61T	SA6.0CA-E3/54
RIBBON_30V	RM4136FK	S1D-E3/61T	SA9.0CA-E3/54
RIBBON_30V_LATC H	RM4136J	S1G-E3/61T	SAB-C167CR-LM HA+
RIBBON_30V_MNT	RM4136W	S1J-E3/61T	SAB-C167CR-LM HA+
RIBBON_34H	RM4558JG	S1PG-E3/84A	SAB-C167SR-LM HA+
RIBBON_34H_LATC H	RMB4S-E3/45	S2800A	SAB-C167SR-LM HA+
RIBBON_34H_MNT	RS1G-E3/5AT	S2800B	SAB-C167SR-LM HA+
RIBBON_34V	RS1K-E3/61T	S2800D	SAB-C167SR-LM HA+
RIBBON_34V_LATC H	RS2D-E3/52T	S2800M	SAC5.0-E3/54
RIBBON_34V_MNT	RS2J-E3/52T	S2G-E3/52T	SAF-C167CR-LM HA+
RIBBON_40H	RS3D-E3/57T	S2SA1774G	SAF-C167CR-LM HA+
RIBBON_40H_LATC H	RTD	S2SC4617G	SAF-C167CR-LM HA+
RIBBON_40H_MNT	RV4136D	S3D-E3/57T	SAF-XC164TM- 4F40F AA
RIBBON_40V	RV4136N	S3M-E3/57T	SAF-XC164TM- 4F40F AA
RIBBON_40V_LATC H	RV4558D	S4PD-M3/86A	SAF-XC866-1FRA AB
RIBBON_40V_MNT	RV4558P	S5227B	SAF-XC866-1FRA AB
RIBBON_50H	S1227-1010BQ	S5227G	SAF-XC866L-1FRA AB
RIBBON_50H_LATC H	S1227-1010BR	S5227J	SAF-XC866L-1FRA AB
RIBBON_50H_MNT	S1227-16BQ	S5227N	SAF-XC866L-1FRA AB
RIBBON_50V	S1227-16BR	SA15AG	SAF-XC866L-1FRA AB
RIBBON_50V_LATC H	S1227-33BQ	SA15ARLG	SA2M-E3/5AT

Multisim 14.1 Base Edition Components

SAF-XC886-6FFA 5V AC	SAF-XC888LM-6FFA 5V AC	SAK-XC2285M-56F80L AA	SAK-XC2287-96F80L AC
SAF-XC886-6FFA 5V AC	SAK-C167CR-LM HA+	SAK-XC2285M-56F80L AA	SAK-XC2287M-104F80L AA
SAF-XC886CLM-6FFA 5V AC	SAK-C167CR-LM HA+	SAK-XC2285M-72F80L AA	SAK-XC2287M-104F80L AA
SAF-XC886CLM-6FFA 5V AC	SAK-C167SR-LM HA+	SAK-XC2285M-72F80L AA	SAK-XC2287M-56F80L AA
SAF-XC886CM-6FFA 5V AC	SAK-C167SR-LM HA+	SAK-XC2286-56F66L AC	SAK-XC2287M-56F80L AA
SAF-XC886CM-6FFA 5V AC	SAK-XC2264-56F66L AC	SAK-XC2286-56F66L AC	SAK-XC2287M-72F80L AA
SAF-XC886LM-6FFA 5V AC	SAK-XC2264-56F66L AC	SAK-XC2286-56F80L AC	SAK-XC2287M-72F80L AA
SAF-XC886LM-6FFA 5V AC	SAK-XC2264-56F80L AC	SAK-XC2286-56F80L AC	SAK-XC2766X-96F66L AC
SAF-XC888-6FFA 5V AC	SAK-XC2264-56F80L AC	SAK-XC2287-56F66L AC	SAK-XC2766X-96F66L AC
SAF-XC888-6FFA 5V AC	SAK-XC2267-56F66L AC	SAK-XC2287-56F66L AC	SAK-XC2786X-96F66L AC
SAF-XC888CLM-6FFA 5V AC	SAK-XC2267-56F66L AC	SAK-XC2287-56F80L AC	SAK-XC2786X-96F66L AC
SAF-XC888CLM-6FFA 5V AC	SAK-XC2267-56F80L AC	SAK-XC2287-56F80L AC	SAK-XC866-1FRA AB
SAF-XC888CM-6FFA 5V AC	SAK-XC2267-56F80L AC	SAK-XC2287-96F66L AC	SAK-XC866-1FRA AB
SAF-XC888CM-6FFA 5V AC	SAK-XC2285M-104F80L AA	SAK-XC2287-96F66L AC	SAK-XC866L-1FRA AB
SAF-XC888LM-6FFA 5V AC	SAK-XC2285M-104F80L AA	SAK-XC2287-96F80L AC	SAK-XC886-6FFA 5V AC

Multisim 14.1 Base Edition Components

SAK-XC886-6FFA 5V AC	SAMPLE_GENERIC	SB520	SBC846ALT1G
	SAMPLE_LOSSY	SB530	SBC846BDW1T1G
SAK-XC886CLM-6FFA 5V AC	SAMPLE_MICROSTRIP	SB540	SBC846BLT1G
SAK-XC886CLM-6FFA 5V AC	SAMPLE_OPENEND	SB540-E3/54	SBC846BLT3G
		SB550	SBC846BPDW1T1G
SAK-XC886CM-6FFA 5V AC	SAMPLE_RFCAP	SB560	SBC846BPDW1T2G
	SAMPLE_RFCOIL	SB560-E3/54	SBC847BDW1T1G
SAK-XC886CM-6FFA 5V AC	SAMPLE_WAVEGUIDE	SBAS16DXV6T1G	SBC847BDW1T3G
SAK-XC886LM-6FFA 5V AC	SB	SBAS20LT1G	SBC856ALT1G
	SB01-15C-TB-E	SBAT54CLT1G	SBC856BDW1T1G
SAK-XC886LM-6FFA 5V AC	SB040-E3/54	SBAV70LT1G	SBC856BDW1T3G
		SBAS70LT3G	SBC856BWT1G
SAK-XC888-6FFA 5V AC	SB05-03Q-TL-E	SBAV99LT1G	SBC857BDW1T1G
	SB1003M3-TL-E	SBAV99LT3G	SBCP56-10T1G
SAK-XC888-6FFA 5V AC	SB140A-E3/54	SBAW56LT1G	SBCP56-16T1G
	SB160-E3/54	SBAW56LT3G	SBCP56-16T3G
SAK-XC888CLM-6FFA 5V AC	SB2H100-E3/54	SBAW56TT1G	SBCP56T1G
SAK-XC888CLM-6FFA 5V AC	SB2H90-E3/23	SBC807-16LT1G	SBCP56T3G
	SB3003CH-TL-E	SBC807-16LT3G	SBCP68T1G
SAK-XC888CM-6FFA 5V AC	SB3003CH-TL-W	SBC807-25LT1G	SBE001-TL-E
SAK-XC888CM-6FFA 5V AC	SB320	SBC807-25LT3G	SBE002-TL-E
	SB330	SBC807-40LT1G	SBR640CTT4G
SAK-XC888LM-6FFA 5V AC	SB340	SBC807-40LT3G	SBR660CTT4G
	SB350	SBC817-25LT1G	SBR80520LT1G
SAK-XC888LM-6FFA 5V AC	SB360	SBC817-25LT3G	SBR80520LT3G
SAMPLE_BEND	SB3H100-E3/54		

Multisim 14.1 Base Edition Components

SBR835LT4G	SBR8120T3G	SEAM-40-03.0-S-06-2-A-K-TR	SEVEN_SEG_DECIMAL_COM_A_BLUE
SBRA8160T3G	SBR8130LT3G		
SBRB1045G	SBR8140T3G	SEAM-40-07.0-S-06-2-A-K-TR	SEVEN_SEG_DECIMAL_COM_A_GREEN
SBRB1045T4G	SBR8190T3G	SEMICONDUCTOR_CAPACITOR_VIRTUAL	SEVEN_SEG_DECIMAL_COM_A_ORANGE
SBRB1545CTG	SBR8320T3G		
SBRB1545CTT4G	SBR8340T3G	SEMICONDUCTOR_RESISTOR_VIRTUAL	SEVEN_SEG_DECIMAL_COM_A_YELLOW
SBRB20200CTT4G	SBS811-TL-E		
SBRB2545CTG	SCH2202-TL-E	SEVEN_SEG_COM_A	SEVEN_SEG_DECIMAL_COM_K
SBRB2545CTT4G	SCHMITT_TRIGGER	SEVEN_SEG_COM_A_BLUE	SEVEN_SEG_DECIMAL_COM_K_BLUE
SBRD81035CTLT4G	SCR	SEVEN_SEG_COM_A_GREEN	SEVEN_SEG_DECIMAL_COM_K_GREEN
SBRD81045T4G	SD05T1G	SEVEN_SEG_COM_A_ORANGE	SEVEN_SEG_DECIMAL_COM_K_ORANGE
SBRD8320G	SD12CT1G	SEVEN_SEG_COM_A_YELLOW	
SBRD8320T4G	SD12T1G		SEVEN_SEG_DECIMAL_COM_K_YELLOW
SBRD8330G	SD241		
SBRD8330T4G	SD41		
SBRD8340G	SDTA114YET1G	SEVEN_SEG_COM_K	SEVEN_SEG_DECIMAL_COM_K_YELLOW
SBRD8340T4G	SDTC114EET1G		
SBRD8350G	SDTC114YET1G	SEVEN_SEG_COM_K_BLUE	SEVEN_SEG_TWO-DIGIT_COM_A
SBRD8350T4G	SDTC124EET1G	SEVEN_SEG_COM_K_GREEN	SEVEN_SEG_TWO-DIGIT_COM_A_BLUE
SBRD8360G	SE10PJ-M3/84A	SEVEN_SEG_COM_K_ORANGE	SEVEN_SEG_TWO-DIGIT_COM_A_GREEN
SBRD8360RLG	SE5534AFK	SEVEN_SEG_COM_K_YELLOW	
SBRD8360T4G	SE5534AJG		SEVEN_SEG_TWO-DIGIT_COM_A_ORANGE
SBRD8835LG	SE5534FK		
SBRD8835LT4G	SE5534JG	SEVEN_SEG_DECIMAL_COM_A	
SBR81100T3G			

Multisim 14.1 Base Edition Components

SEVEN_SEG_TWO-DIGIT_COM_A_YELLOW	SFH6136-X009T	SFH6701-X007	SFT1440-E
	SFH6136-X016	SFH6701-X009	SFT1440-H
SEVEN_SEG_TWO-DIGIT_COM_K	SFH6136-X017T	SFH6702	SFT1440-TL-E
	SFH6136-X018	SFH6702-X006	SFT1440-TL-H
SEVEN_SEG_TWO-DIGIT_COM_K_BLUE	SFH6136-X019T	SFH6702-X007	SGL41-40-E3/96
	SFH6156-3	SFH6702-X009T	SHIFT_4BIDI
SEVEN_SEG_TWO-DIGIT_COM_K_GREEN	SFH6156-3T	SFH6705	SHIFT_4PIPO
	SFH615A-3	SFH6705-X006	SHIFT_8PIN
SEVEN_SEG_TWO-DIGIT_COM_K_ORANGE	SFH615A-3X001	SFH6705-X007	SHIFT_8POUT
	SFH615A-3X006	SFH6711	SI2302DS
SEVEN_SEG_TWO-DIGIT_COM_K_YELLOW	SFH615A-3X007T	SFH6711-X007	SI2304DS
	SFH615A-3X009T	SFH6712	SJ1-3515N
	SFH615A-3X016	SFH6712-X007	SL05T1G
SFH 203 FA	SFH615A-3X017	SFH6719	SL12-E3/5AT
SFH 205 F	SFH617A-3	SFH6720T	SL13-E3/61T
SFH 206 K	SFH617A-3X001	SFH6721T	SL22-E3/52T
SFH 213	SFH617A-3X006	SFH6755T	SL23-E3/52T
SFH 229 FA	SFH617A-3X007T	SFH6756T	SL43-E3/57T
SFH 2400 FA	SFH617A-3X016	SFH6757T	SL44-E3/57T
SFH 2500 FA-Z	SFH617A-3X017T	SFH690CT	SLOW_1A
SFH 2505 FA-Z	SFH6316T	SFH690C-X001T	SLOW_2A
SFH6136	SFH6343T	SFT1341-E	SLOW_3A
SFH6136-X001	SFH6700	SFT1341-TL-E	SLOW_4A
SFH6136-X006	SFH6700-X009	SFT1423-E	SM05T1G
SFH6136-X007	SFH6701	SFT1423-TL-E	SM12T1G

Multisim 14.1 Base Edition Components

SM15T150A-E3/57T	SM8S26AHE3/2D	SMBJ170A-E3/52	SMBT2907A
SM15T150CA-E3/9AT	SM8S30AHE3/2D	SMBJ170CA-E3/52	SMBT35200MT1G
SM15T18A-E3/57T	SM8S33AHE3/2D	SMBJ188CA-E3/52	SMBT3904
SM15T24A-E3/9AT	SM8S36AHE3/2D	SMBJ22A-E3/52	SMBT3906
SM15T33A-E3/57T	SM8S43AHE3/2D	SMBJ24CA-E3/52	SMBT3946DW1T1G
SM15T68A-E3/57T	SMAJ28A-E3/61	SMBJ26CA-E3/52	SMBTA06
SM15T68CA-E3/57T	SMAJ11A-E3/61	SMBJ28CA-E3/52	SMBTA42
SM3G45	SMAJ11CA-E3/61	SMBJ30A-E3/52	SMBTA56
SM3J45	SMAJ12A-E3/61	SMBJ33A-E3/52	SMBTA56C
SM5S20AHE3/2D	SMAJ12CA-E3/61	SMBJ33CA-E3/52	SMBTA92
SM5S22AHE3/2D	SMAJ150CA-E3/61	SMBJ36A-E3/52	SMCJ12A-E3/57T
SM5S26AHE3/2D	SMAJ15A-E3/61	SMBJ36CA-E3/52	SMCJ130CA-E3/57T
SM5S33AHE3/2D	SMAJ16A-E3/61	SMBJ3V3-E3/52	SMCJ15A-E3/57T
SM5S36AHE3/2D	SMAJ24A-E3/61	SMBJ45A-E3/52	SMCJ15CA-E3/57T
SM6S33AHE3/2D	SMAJ24CA-E3/61	SMBJ48A-E3/52	SMCJ16CA-E3/57T
SM6T12A-E3/52	SMAJ26A-E3/61	SMBJ48CA-E3/52	SMCJ18A-E3/57T
SM8S12AHE3/2D	SMAJ28CA-E3/61	SMBJ5.0CA-E3/52	SMCJ18CA-E3/57T
SM8S14AHE3/2D	SMAJ36A-E3/61	SMBJ58A-E3/52	SMCJ26CA-E3/57T
SM8S15AHE3/2D	SMAJ40CA-E3/61	SMBJ58CA-E3/52	SMCJ28CA-E3/57T
SM8S16AHE3/2D	SMAJ530-E3/61	SMBJ6.0A-E3/52	SMCJ30CA-E3/57T
SM8S17AHE3/2D	SMAJ6.5A-E3/61	SMBJ70A-E3/52	SMCJ33CA-E3/57T
SM8S18AHE3/2D	SMAJ60A-E3/61	SMBJ8.0A-E3/52	SMCJ36CA-E3/57T
SM8S22AHE3/2D	SMB8J28CA-E3/52	SMBJ8.0CA-E3/52	SMCJ48CA-E3/57T
SM8S24AHE3/2D	SMBJ14A-E3/52	SMBJ85A-E3/52	SMCJ5.0CA-E3/57T
	SMBJ15CA-E3/52	SMBT2222A	SMCJ51CA-E3/57T

Multisim 14.1 Base Edition Components

SMCJ58A-E3/57T	SMF7.5AT1G	SML4758	SMMBTA06LT1G
SMCJ6.5A-E3/57T	SMF8.0AT1G	SML4759	SMMBTA06LT3G
SMCJ75A-E3/57T	SML4735	SML4760	SMMBTA06WT1G
SMCJ78A-E3/57T	SML4736	SML4761	SMMBTA14LT1G
SMCJ8.5A-E3/57T	SML4737	SML4762	SMMBTA42LT1G
SMF05CT1G	SML4738	SML4763	SMMBTA42LT3G
SMF05CT2G	SML4739	SMMBD2837LT1G	SMMBTA56LT1G
SMF12AT1G	SML4740	SMMBD301LT3G	SMMBTA56LT3G
SMF12CT1G	SML4741	SMMBD7000LT1G	SMMBTA92LT1G
SMF15CT1G	SML4742	SMMBD7000LT3G	SMMBTA92LT3G
SMF18AT1G	SML4743	SMMBD770T1G	SMMDL914T1G
SMF22AT1G	SML4744	SMMBD914LT1G	SMMJT350T1G
SMF24AT1G	SML4745	SMMBD914LT3G	SMMSD301T1G
SMF24CT1G	SML4746	SMMBT2222ALT1G	SMMSD4148T1G
SMF26AT1G	SML4747	SMMBT2222ALT3G	SMMSD4148T3G
SMF28AT1G	SML4748	SMMBT2369ALT1G	SMMUN2111LT1G
SMF30AT1G	SML4749	SMMBT2907ALT1G	SMMUN2111LT3G
SMF33AT1G	SML4750	SMMBT2907ALT3G	SMMUN2113LT1G
SMF36AT1G	SML4751	SMMBT3904LT1G	SMMUN2114LT1G
SMF48AT1G	SML4752	SMMBT3904TT1G	SMMUN2116LT1G
SMF5.0AT1G	SML4753	SMMBT4401LT1G	SMMUN2116LT3G
SMF58AT1G	SML4754	SMMBT4403LT1G	SMMUN2134LT1G
SMF6.0AT1G	SML4755	SMMBT5401LT1G	SMMUN2211LT1G
SMF6.5AT1G	SML4756	SMMBT5551LT1G	SMMUN2211LT3G
SMF7.0AT1G	SML4757	SMMBT5551LT3G	SMMUN2213LT1G

Multisim 14.1 Base Edition Components

SMMUN2213LT3G	SMUN5115DW1T1 G	SMUN5237DW1T1 G	SNSS40600CF8T1G
SMMUN2214LT1G			SONALERT
SMMUN2215LT1G	SMUN5115T1G	SMUN5311DW1T2 G	SPB08P06P G
SMMUN2216LT1G	SMUN5116DW1T1 G	SMUN5312DW1T1 G	SPB100N03S2-03 G
SMMUN2216LT3G	SMUN5133T1G		SPB18P06P G
SMMUN2233LT1G	SMUN5211T1G	SMUN5313DW1T1 G	SPB80P06P G
SMMUN2234LT1G	SMUN5211T3G	SMUN5314DW1T1 G	SPD04P10PL G
SMS05T1G	SMUN5212T1G		SPD08P06P G
SMUN2111T1G	SMUN5213DW1T1 G	SMUN5315DW1T1 G	SPD09P06PL G
SMUN2111T3G			SPD15P10P G
SMUN2114T1G	SMUN5213T1G	SMUN5330DW1T1 G	SPD15P10PL G
SMUN2211T1G	SMUN5214DW1T1 G	SMUN5335DW1T1 G	SPD18P06P G
SMUN2211T3G	SMUN5214T1G		SPD30N03S2L-07 G
SMUN2216T1G	SMUN5215T1G	SMUN5335DW1T2 G	SPD30N03S2L-10 G
SMUN2230T1G	SMUN5216DW1T1 G		SPD30N03S2L-20 G
SMUN2232T1G		SN10502D	SPD30P06P G
SMUN2240T1G	SMUN5230DW1T1 G	SN10502DGK	SPD50N03S2-07 G
SMUN5112DW1T1 G	SMUN5232DW1T1 G	SN10502DGN	SPD50N03S2L-06 G
SMUN5112T1G		SN200501036DRE4	SPD50P03L G
	SMUN5232T1G	SN412008DRE4	SPDT
SMUN5113DW1T1 G	SMUN5233DW1T1 G	SN7002N	SPDT_CLOSED
SMUN5113T1G		SN7002W	SPDT_OPEN
SMUN5114DW1T1 G	SMUN5233T1G	SN74LVC2G66QDC URQ1	SPEED_F
SMUN5114T1G	SMUN5235DW1T1 G	SNSS30201MR6T1G	SPEED_FR
		SNSS35200MR6T1G	SPP08P06P H

Multisim 14.1 Base Edition Components

SPP15P10P H	SR_FF	SS26T3G	SSM2017P
SPP15P10PL H	SR_FF_NEGSR	SS2H10-E3/2CT	SSM2017S
SPP18P06P H	SR_FF_POSSR	SS2P3L-M3/84A	SSM2135S
SPP80P06P H	SR_LATCH	SS2P4-M3/84A	SSM2212RZ
SPST	SR_LATCH_NEGSR	SS2PH10-M3/84A	SSM2212RZ-R7
SPST_CLOSED	SS0503SH-TL-E	SS32	SSM2212RZ-RL
SPST_NC_DB	SS10P3-M3/86A	SS32-E3/57T	SSRD8620CTRG
SPST_NC_SB	SS10P4-M3/86A	SS33	SSRD8620CTT4G
SPST_NO_DB	SS10P6-M3/86A	SS34	SSRD8620CTT4RG
SPST_NO_SB	SS10PH10-M3/86A	SS34-E3/57T	ST10F168-PQFP(144)
SPST_OPEN	SS14-E3/61T	SS35	ST10F269T3-TQFP(144)
SPZT2222AT1G	SS16-E3/61T	SS36-E3/57T	ST10R272L-TQFP(100)
SPZT2907AT1G	SS16T3G	SS3H9-E3/57T	ST5771-1
SPZT651T1G	SS1H10-E3/5AT	SS3P4HM3/84A	ST7263B-SDIP(32)
SPZTA42T1G	SS1P3L-M3/84A	SS3P4LHM3/86A	ST7263B-SO(34)
SR_4BIDI	SS1P4L-M3/84A	SS3P6-E3/84A	STD110N02RT4G
SR_4P_P_3SO	SS1P4-M3/84A	SS5P10-M3/86A	STD24N06LT4G
SR_4P_P_INV	SS1P6L-E3/84A	SS5P6-M3/86A	STD2955T4G
SR_4S_P	SS22T3G	SS8P3L-M3/86A	STD5406NT4G
SR_8P_2S	SS24-E3/52T	SS8PH10-M3/86A	STD5407NT4G
SR_8P_S	SS24S-E3/61T	SSA24-E3/61T	STEP_CURRENT
SR_8P_S_C	SS24T3	SSA33L-E3/61T	STEP_VOLTAGE
SR_8PS_S_AS_L	SS24T3G	SSA34-E3/61T	STP32N06L
SR_8PS_S_SL	SS26-E3/52T	SSC53L-E3/57T	
SR_8S_P	SS26T3	SSC54-E3/57T	

Multisim 14.1 Base Edition Components

SUR620CTT4G	SURS360DBT3G	SZ1SMA5921BT3G	SZ1SMB5931BT3G
SUR81520G	SURS360DT3G	SZ1SMA5922BT3G	SZ1SMB5933BT3G
SUR81560G	SURS8105T3G	SZ1SMA5927BT3G	SZ1SMB5934BT3G
SUR83020PTG	SURS8110T3G	SZ1SMA5932BT3G	SZ1SMB5935BT3G
SUR83060PTG	SURS8115T3G	SZ1SMA5936BT3G	SZ1SMB5936BT3G
SUR8820G	SURS8120T3G	SZ1SMA5940BT3G	SZ1SMB5937BT3G
SUR8840G	SURS8140T3G	SZ1SMB14AT3G	SZ1SMB5939BT3G
SURA8110T3G	SURS8160T3G	SZ1SMB24AT3G	SZ1SMC36AT3G
SURA8120T3G	SURS8205T3G	SZ1SMB24CAT3G	SZBZX84B16LT1G
SURA8130T3G	SURS8210T3G	SZ1SMB26CAT3G	SZBZX84C12LT1G
SURA8140T3G	SURS8220T3G	SZ1SMB28AT3G	SZBZX84C15LT1G
SURA8160T3G	SURS8320T3G	SZ1SMB28CAT3G	SZBZX84C15LT3G
SURA8210T3G	SURS8340T3G	SZ1SMB30AT3G	SZBZX84C33LT1G
SURA8215T3G	SURS8360BT3G	SZ1SMB30CAT3G	SZBZX84C33LT3G
SURA8220T3G	SURS8360T3G	SZ1SMB33CAT3G	SZBZX84C36LT1G
SURA8240T3G	SZ1.5SMC15AT3G	SZ1SMB5.0AT3G	SZBZX84C3V0LT1G
SURB1620CTT4G	SZ1.5SMC20AT3G	SZ1SMB58CAT3G	SZBZX84C4V7LT1G
SURD8320T4G	SZ1.5SMC33AT3G	SZ1SMB5918BT3G	SZBZX84C4V7LT3G
SURD8330T4G	SZ1.5SMC39AT3G	SZ1SMB5919BT3G	SZBZX84C5V1LT1G
SURD8530T4G	SZ1.5SMC43AT3G	SZ1SMB5920BT3G	SZBZX84C5V1LT3G
SURHB8840CTT4G	SZ1.5SMC62AT3G	SZ1SMB5921BT3G	SZBZX84C5V6LT1G
SURHD8560T4G	SZ1SMA30AT3G	SZ1SMB5922BT3G	SZBZX84C5V6LT3G
SURHD8560W1T4G	SZ1SMA40CAT3G	SZ1SMB5924BT3G	SZBZX84C68LT1G
SURHS8160T3G	SZ1SMA5913BT3G	SZ1SMB5925BT3G	SZBZX84C6V2LT1G
SURS340DT3G	SZ1SMA5918BT3G	SZ1SMB5927BT3G	SZBZX84C6V2LT3G

Multisim 14.1 Base Edition Components

SZBZX84C6V8LT1G	SZMM5Z20VT1G	SZMMBZ5221BLT1 G	SZMMSZ3V3T1G
SZBZX84C6V8LT3G	SZMM5Z24VT1G		SZMMSZ4678T1G
SZBZX84C75LT1G	SZMM5Z27VT1G	SZMMBZ5222BLT1 G	SZMMSZ4683T1G
SZBZX84C9V1LT1G	SZMM5Z36VT1G	SZMMBZ5226BLT1 G	SZMMSZ4688T1G
SZBZX84C9V1LT3G	SZMM5Z3V0T1G		SZMMSZ4689T1G
SZESD5Z5.0T1G	SZMM5Z3V3T1G	SZMMBZ5231BLT1 G	SZMMSZ4690T1G
SZESD5Z7.0T1G	SZMM5Z4V7ST1G		SZMMSZ4690T3G
SZESD9B5.0ST5G	SZMM5Z4V7ST5G	SZMMBZ5231BLT3 G	SZMMSZ4691T1G
SZMM3Z10VT1G	SZMM5Z5V1T1G	SZMMBZ5232BLT1 G	SZMMSZ4692T1G
SZMM3Z12VST1G	SZMM5Z5V6ST1G		SZMMSZ4696T1G
SZMM3Z15VT1G	SZMM5Z5V6T1G	SZMMBZ5240BLT1 G	SZMMSZ4699T1G
SZMM3Z18VT1G	SZMM5Z6V2ST1G	SZMMBZ5242BLT1 G	SZMMSZ4705T1G
SZMM3Z20VT1G	SZMM5Z6V8ST1G		SZMMSZ4715T1G
SZMM3Z2V4T1G	SZMM5Z6V8T1G	SZMMBZ5248BLT1 G	SZMMSZ5221BT1G
SZMM3Z3V3ST1G	SZMM5Z7V5T1G		SZMMSZ5225BT1G
SZMM3Z3V6T1G	SZMM5Z8V2ST1G	SZMMBZ5254BLT1 G	SZMMSZ5226BT1G
SZMM3Z43VT1G	SZMM5Z8V2T1G	SZMMBZ5256BLT1 G	SZMMSZ5228BT1G
SZMM3Z4V3ST1G	SZMMBZ15VDLT1G		SZMMSZ5231BT1G
SZMM3Z4V7T1G	SZMMBZ15VDLT3G	SZMMBZ5V6ALT1G	SZMMSZ5234BT1G
SZMM3Z5V1T1G	SZMMBZ20VALT1G	SZMMQA15VT1G	SZMMSZ5235BT1G
SZMM3Z5V6ST1G	SZMMBZ27VALT1G	SZMMQA5V6T1G	SZMMSZ5236BT1G
SZMM5Z10VT1G	SZMMBZ27VALT3G	SZMMQA6V2T1G	SZMMSZ5239BT1G
SZMM5Z12VT1G	SZMMBZ27VCLT1G	SZMMSZ10T1G	SZMMSZ5240BT1G
SZMM5Z16VT1G	SZMMBZ33VALT1G	SZMMSZ12T1G	SZMMSZ5242BT1G
SZMM5Z18VT1G		SZMMSZ2V7T1G	SZMMSZ5242BT3G

Multisim 14.1 Base Edition Components

SZMMSZ5243BT1G	SZP6SMB62AT3G	TC1411NEUA	TC4420CAT
SZMMSZ5245BT1G	SZSMF12CT1G	TC1411NVOA	TC4420COA
SZMMSZ5246BT1G	SZSMF33AT1G	TC1411NVPA	TC4420CPA
SZMMSZ5254BT1G	T_FF	TC1411NVUA	TC4420EMF
SZMMSZ5258BT1G	T_FF_NEGSR	TC1411VOA	TC4420EOA
SZMMSZ5258BT3G	TC1410COA	TC1411VPA	TC4420EPA
SZMMSZ5259BT1G	TC1410CPA	TC1411VUA	TC4420IJA
SZMMSZ5260BT1G	TC1410EOA	TC1412COA	TC4420MJA
SZMMSZ5262BT1G	TC1410EPA	TC1412CPA	TC4420VAT
SZMSQA6V1W5T2G	TC1410EUA	TC1412EOA	TC4420VMF
SZNUP1105LT1G	TC1410NCOA	TC1412EPA	TC4420VOA
SZNUP1301ML3T1G	TC1410NCPA	TC1412EUA	TC4420VPA
SZNUP2105LT1G	TC1410NEOA	TC1412NCOA	TC4421AVMF
SZNUP4301MR6T1 G	TC1410NEPA	TC1412NCPA	TC4421CAT
	TC1410NEUA	TC1412NEOA	TC4421CPA
SZNUP4304MR6T1 G	TC1410NVUA	TC1412NEPA	TC4421EMF713
	TC1411COA	TC1412NEUA	TC4421EPA
SZNZ9F2V7ST5G	TC1411CPA	TC4404COA	TC4421ESM
SZNZ9F6V2ST5G	TC1411EOA	TC4404CPA	TC4421MJA
SZP6SMB15AT3G	TC1411EPA	TC4404EOA	TC4421VAT
SZP6SMB18AT3G	TC1411EUA	TC4404EPA	TC4421VMF
SZP6SMB20AT3G	TC1411NCOA	TC4405COA	TC4421VPA
SZP6SMB33AT3G	TC1411NCPA	TC4405CPA	TC4422CAT
SZP6SMB43CAT3G	TC1411NEOA	TC4405EOA	TC4422CPA
SZP6SMB51AT3G	TC1411NEPA	TC4405EPA	TC4422EAT
SZP6SMB6.8AT3G			

Multisim 14.1 Base Edition Components

TC4422EPA	TC4424EOE	TC4426MJA	TC4428VOA
TC4422ESM	TC4424EPA	TC4426VMF	TC4428VUA
TC4422MJA	TC4424MJA	TC4426VUA	TC4429COA713
TC4422VAT	TC4424VMF	TC4427ACOA713	TC4429EMF
TC4422VMF	TC4424VOE	TC4427AEOA713	TC4429EOA713
TC4422VPA	TC4424VPA	TC4427COA	TC4429IJA
TC4423AVMF	TC4425AVMF	TC4427CPA	TC4429MJA
TC4423AVOA	TC4425AVOA	TC4427EMF	TC4429VAT
TC4423AVOE	TC4425AVOE	TC4427EOA	TC4429VMF
TC4423AVPA	TC4425AVPA	TC4427EPA	TC4429VOA
TC4423COE	TC4425COE	TC4427EUA713	TC4429VPA
TC4423CPA	TC4425CPA	TC4427VMF	TC4431COA
TC4423EOE	TC4425EOE	TC4427VOA	TC4431CPA
TC4423EPA	TC4425EPA	TC4427VUA	TC4431EOA
TC4423MJA	TC4425VMF	TC4428ACOA713	TC4431EPA
TC4423VMF	TC4425VOE	TC4428AEJA	TC4431VOA
TC4423VOE	TC4425VPA	TC4428AEOA713	TC4431VPA
TC4423VPA	TC4426ACOA713	TC4428AMJA	TC4432COA
TC4424AVMF	TC4426AEOA713	TC4428COA	TC4432CPA
TC4424AVOA	TC4426COA	TC4428CPA	TC4432EOA
TC4424AVOE	TC4426CPA	TC4428EMF	TC4432EPA
TC4424AVPA	TC4426EMF	TC4428EOA	TC4432VOA
TC4424COE	TC4426EOA	TC4428EPA	TC4432VPA
TC4424CPA	TC4426EPA	TC4428EUA	TC4451VAT
TC4424EMF	TC4426EUA	TC4428VMF	TC4451VMF

Multisim 14.1 Base Edition Components

TC4451VOA	TD_SW1	TDZ2V7J	TEMPLATE_1P1S_T MODEL
TC4451VPA	TDA2030	TDZ30J	
TC4452VAT	TDE1890_SO20	TDZ3V0J	TEMPLATE_1P2S_C OUPLED
TC4452VMF	TDE1890_ZIP11	TDZ3V3J	TEMPLATE_1P2S_N ON_LINEAR
TC4452VOA	TDE1891_SIP11	TDZ3V6J	
TC4452VPA	TDE1891_ZIP11	TDZ3V9J	TEMPLATE_1P2S_T AP_TMODEL
TC4467COE	TDE1897C_DIP8	TDZ4V3J	
TC4467CPD	TDE1897C_SO20	TDZ4V7J	TEMPLATE_1P2S_T MODEL
TC4467EOE713	TDE1898C_DIP8	TDZ5V1J	TEST_LABEL
TC4468COE	TDE1898C_SIP9	TDZ5V6J	TEST_PT_SMT
TC4468CPD	TDE1898C_SO20	TDZ6V2J	TEST_PT_THT
TC4468EOE713	TDM_CURRENT	TDZ6V8J	TF408-2-TL-H
TC4468MOE	TDM_VOLTAGE	TDZ7V5J	TF408-3-TL-H
TC4469COE	TDZ10J	TDZ8V2J	TF410-TL-H
TC4469CPD	TDZ11J	TDZ9V1J	TF412ST5G
TC4469EJD	TDZ12J	TEMD1000	TF414T5G
TC4469MJD	TDZ13J	TEMD1020	THERMAL_NOISE
TCET1100	TDZ15J	TEMD1030	THERMAL_OL
TCET1100G	TDZ16J	TEMD5010X01	THERMAL_OL_REL Y
TCET1600	TDZ18J	TEMD5020X01	
TCET1600G	TDZ20J	TEMD5110X01	THREE_PHASE_DEL TA
TCLT1003	TDZ22J	TEMD5510FX01	THREE_PHASE_WYE
TCMT1103	TDZ24J	TEMD6010FX01	THS3001CD
TCMT1600	TDZ27J	TEMP_NC	THS3001CDGN
TCMT4600	TDZ2V4J	TEMP_NO	THS3001ID

Multisim 14.1 Base Edition Components

THS3001IDGN	THS3112ID	THS4011CDGN	THS4041CDGN
THS3061D	THS3112IDDA	THS4011ID	THS4041ID
THS3061DGN	THS3120CDGN	THS4011MFKB	THS4041IDGN
THS3062D	THS3120DGN	THS4012CD	THS4042CD
THS3062DDA	THS3120ID	THS4012CDGN	THS4042CDGN
THS3062DGN	THS3120IDGN	THS4012ID	THS4042ID
THS3091D	THS3121CD	THS4021CD	THS4042IDGN
THS3091DDA	THS3121ID	THS4021CDGN	THS4051CD
THS3092D	THS3121IDGN	THS4021ID	THS4051CDGN
THS3092DDA	THS3122CD	THS4021IDGN	THS4051ID
THS3095D	THS3122CDDA	THS4022CD	THS4051IDGN
THS3095DDA	THS3122ID	THS4022CDGN	THS4051MFK
THS3096D	THS3122IDDA	THS4022ID	THS4051MJG
THS3096PWP	THS3125CPWP	THS4022IDGN	THS4052CD
THS3110DGN	THS3125ID	THS4031CD	THS4052CDGN
THS3110ID	THS3125IPWP	THS4031CDGN	THS4052ID
THS3110IDGN	THS3201D	THS4031ID	THS4052IDGN
THS3110IDR	THS3201DBVT	THS4031IDGN	THS4061CD
THS3111CD	THS3201DGK	THS4031MFK	THS4061CDGN
THS3111CDGNR	THS3202D	THS4031MJG	THS4061ID
THS3111DGN	THS3202DGK	THS4032CD	THS4061IDGN
THS3111ID	THS3202DGN	THS4032CDGN	THS4061MFK
THS3111IDGN	THS4001CD	THS4032ID	THS4061MJG
THS3112CD	THS4001ID	THS4032IDGN	THS4062CD
THS3112CDDA	THS4011CD	THS4041CD	THS4062CDGN

Multisim 14.1 Base Edition Components

THS4062ID	THS4140IDGK	THS4222DGK	THS4501CD
THS4062IDGN	THS4141CD	THS4222DGN	THS4501CDGK
THS4081CD	THS4141CDGK	THS4225D	THS4501CDGN
THS4081CDGN	THS4141ID	THS4225DGK	THS4501ID
THS4081ID	THS4141IDGK	THS4225DGN	THS4501IDGK
THS4081IDGN	THS4150CD	THS4226DGQ	THS4501IDGN
THS4082CD	THS4150CDGK	THS4271D	THS4502CD
THS4082CDGN	THS4150ID	THS4271DGK	THS4502CDGK
THS4082ID	THS4150IDGK	THS4271DGN	THS4502ID
THS4082IDGN	THS4151CD	THS4271DR	THS4502IDGK
THS4120CD	THS4151CDGK	THS4271DRBT	THS4503CD
THS4120CDGK	THS4151ID	THS4281D	THS4503CDGK
THS4121CD	THS4151IDGK	THS4281DBVR	THS4503CDGN
THS4121CDGK	THS4211D	THS4281DGK	THS4503ID
THS4130CD	THS4211DGK	THS4302RGTT	THS4503IDGK
THS4130CDGK	THS4211DGN	THS4303RGTT	THS4503IDGN
THS4130ID	THS4215D	THS4304D	THS4504D
THS4130IDGK	THS4215DGK	THS4304DBVT	THS4504DGK
THS4131CD	THS4215DGN	THS4304DGK	THS4504DGN
THS4131CDGK	THS4215DRBT	THS4500CD	THS4505D
THS4131ID	THS4221D	THS4500CDGK	THS4505DGK
THS4131IDGK	THS4221DBV	THS4500CDGN	THS4508RGTR
THS4140CD	THS4221DGK	THS4500ID	THS4509RGT
THS4140CDGK	THS4221DGN	THS4500IDGK	THS4511RGTT
THS4140ID	THS4222D	THS4500IDGN	THS4513RGTR

Multisim 14.1 Base Edition Components

THS4520RGTR	THS6022CPWP	THS6092ID	TIMED_NCTO
THS4531AID	THS6022IPWP	THS6092IDDA	TIMED_NOTC
THS4531AIDGK	THS6042CDDA	THS6093CPWP	TIMED_NOTO
THS4531AIRUNT	THS6042ID	THS6093ID	TI-MSP430-HDR
THS4531ID	THS6042IDDA	THS6093IPWP	TIP100G
THS4531IDGK	THS6043CD	THS6182D	TIP101G
THS4531IRUNT	THS6043CPWP	THS6182DW	TIP102G
THS4532IPW	THS6043ID	THS6182DWP	TIP106G
THS4541IRGTR	THS6043IPWP	THS6182RHFR	TIP107G
THS4541IRUNR	THS6052CD	THS7001CPWP	TIP110G
THS4601CD	THS6052CDDA	THS7001IPWP	TIP111G
THS4601CDDA	THS6052ID	THS7002CPWP	TIP112G
THS4601CDG4	THS6052IDDA	THS7002IPWP	TIP115G
THS4601ID	THS6053CPWPR	THS7530PWP	TIP116G
THS4601IDDA	THS6053ID	TIME_DELAY_1A	TIP117G
THS4601IDG4	THS6053IPWP	TIME_DELAY_1C	TIP120G
THS4631D	THS6062CD	TIME_DELAY_2A	TIP121G
THS4631DDA	THS6062CDGN	TIME_DELAY_2C	TIP122G
THS4631DGN	THS6062ID	TIME_DELAY_3A	TIP125G
THS6002CDWP	THS6062IDGN	TIME_DELAY_3C	TIP126G
THS6002IDWP	THS6072CD	TIME_DELAY_4A	TIP127G
THS6007IPWP	THS6072CDGN	TIME_DELAY_4C	TIP140G
THS6012CDWP	THS6072ID	TIME_DELAY_NC	TIP141G
THS6012IDWP	THS6072IDGNR	TIME_DELAY_NO	TIP142G
THS6012IGQER	THS6092CDDA	TIMED_NCTC	TIP147G

Multisim 14.1 Base Edition Components

TIP2955G	TIP42G	TL031MFK	TL034AMD
TIP29AG	TIP47G	TL031MJG	TL034AMFK
TIP29BG	TIP48G	TL031MP	TL034AMJ
TIP29CG	TIP50G	TL032ACD	TL034AMN
TIP3055G	TIS92	TL032ACP	TL034CD
TIP30CG	TIS93	TL032AID	TL034CN
TIP31AG	TIS97	TL032AIP	TL034ID
TIP31BG	TIS98	TL032AMD	TL034IN
TIP31CG	TIS99	TL032AMFK	TL034MD
TIP31G	TL022CD	TL032AMJG	TL034MFK
TIP32AG	TL022CP	TL032AMJL	TL034MJ
TIP32BG	TL022MJG	TL032AMP	TL034MN
TIP32CG	TL022MU	TL032CD	TL044CJ
TIP32G	TL031ACD	TL032CP	TL044CN
TIP33CG	TL031ACP	TL032ID	TL044MFK
TIP35AG	TL031AID	TL032IP	TL044MJ
TIP35CG	TL031AIP	TL032MD	TL044MW
TIP36AG	TL031AMD	TL032MFK	TL051ACD
TIP36CG	TL031AMFK	TL032MJG	TL051ACP
TIP41AG	TL031AMJG	TL032ML	TL051AID
TIP41BG	TL031AML	TL032MP	TL051AIP
TIP41CG	TL031AMP	TL034ACD	TL051AMD
TIP42AG	TL031ID	TL034ACN	TL051AMFK
TIP42BG	TL031IP	TL034AID	TL051AMJG
TIP42CG	TL031MD	TL034AIN	TL051AML

Multisim 14.1 Base Edition Components

TL051AMP	TL052MJG	TL061ID	TL064ACN
TL051CD	TL052ML	TL061IP	TL064BCD
TL051CP	TL052MP	TL061MFK	TL064BCN
TL051ID	TL054ACD	TL061MJG	TL064CD
TL051IP	TL054ACN	TL061ML	TL064CN
TL051MD	TL054AID	TL061MU	TL064CNSR
TL051MFK	TL054AIN	TL061VD	TL064CPW
TL051MJG	TL054AMD	TL061VP	TL064ID
TL051ML	TL054AMFK	TL062ACD	TL064IN
TL051MP	TL054AMJ	TL062ACP	TL064MFK
TL052ACD	TL054AMN	TL062ACPSR	TL064MJ
TL052ACP	TL054CD	TL062BCD	TL064MW
TL052AID	TL054CN	TL062BCP	TL066ACD
TL052AIP	TL054ID	TL062CD	TL066ACP
TL052AMD	TL054IN	TL062CP	TL066CD
TL052AMFK	TL054MD	TL062CPSR	TL066CP
TL052AMJG	TL054MFK	TL062CPW	TL066ID
TL052AML	TL054MJ	TL062ID	TL066IP
TL052AMP	TL054MN	TL062IP	TL066MFK
TL052CD	TL061ACD	TL062IPW	TL066MJG
TL052CP	TL061ACP	TL062MFK	TL070ACD
TL052ID	TL061BCD	TL062MJG	TL070ACJG
TL052IP	TL061BCP	TL062ML	TL070ACP
TL052MD	TL061CD	TL062MU	TL070CD
TL052MFK	TL061CP	TL064ACD	TL070CJG

Multisim 14.1 Base Edition Components

TL070CP	TL072BCP	TL074MW	TL082CP
TL070CPW	TL072CD	TL075	TL082ID
TL070ID	TL072CP	TL075CN	TL082IP
TL070IJG	TL072CPSR	TL080CD	TL082IPWR
TL070IP	TL072CPW	TL080CP	TL082MFK
TL070MD	TL072CPWLE	TL080M	TL082MJG
TL070MP	TL072ID	TL081ACD	TL083
TL071ACD	TL072IP	TL081ACJG	TL084ACD
TL071ACJG	TL072MFK	TL081ACP	TL084ACN
TL071ACP	TL072MJG	TL081AMJG	TL084ACNSR
TL071BCD	TL072MJGB	TL081BCD	TL084BCD
TL071BCP	TL072ML	TL081BCJG	TL084BCN
TL071CD	TL072MP	TL081BCP	TL084CD
TL071CJG	TL074ACD	TL081CD	TL084CN
TL071CP	TL074ACN	TL081CJG	TL084CNSR
TL071CPWLE	TL074BCD	TL081CP	TL084CPW
TL071ID	TL074BCN	TL081CPW	TL084ID
TL071IP	TL074CD	TL081ID	TL084IN
TL071MFK	TL074CN	TL081IJG	TL084MFK
TL071MJG	TL074CPWLE	TL081IP	TL084MJ
TL071ML	TL074ID	TL081MFK	TL085
TL072ACD	TL074IN	TL081MJG	TL087CD
TL072ACP	TL074MFK	TL081MU	TL087CJG
TL072ACPSR	TL074MJ	TL082CD	TL087CL
TL072BCD	TL074MN	TL082CM	TL087CP

Multisim 14.1 Base Edition Components

TL087ID	TL288CL	TL3474CN	TLC074CD
TL087IJG	TL288CP	TL3474CPW	TLC074CN
TL087IL	TL288MJG	TL3474ID	TLC074CPWP
TL087IP	TL288ML	TL3474IN	TLC081CD
TL088CD	TL288MU	TL3474IPW	TLC081CP
TL088CJG	TL321CD	TL35071D	TLC081ID
TL088CL	TL321CP	TL35071P	TLC081IP
TL088CP	TL321ID	TL431ACD	TLC1078CD
TL088ID	TL321IP	TL431ACLP	TLC1078CP
TL088IJG	TL322CD	TL431ACP	TLC1078ID
TL088IL	TL322CDR	TL431BCD	TLC1078IP
TL088IP	TL322CP	TL431BCLP	TLC1078MD
TL088MJG	TL322ID	TL431BCP	TLC1078MFK
TL088ML	TL322IP	TL972ID	TLC1078MJG
TL088MU	TL33071D	TL972IDGKR	TLC1078MP
TL136	TL33071P	TL972IP	TLC1079CD
TL136N	TL331IDBVR	TL972IPW	TLC1079CN
TL1963ADCQR	TL331KDBVR	TLC070CD	TLC1079ID
TL1963AKTTR	TL34071D	TLC070CP	TLC1079IN
TL287CD	TL34071P	TLC070ID	TLC1079MD
TL287CJG	TL3472CD	TLC070IP	TLC1079MFK
TL287CL	TL3472CP	TLC071CD	TLC1079MJ
TL287CP	TL3472ID	TLC071CP	TLC1079MN
TL288CD	TL3472IP	TLC071ID	TLC2201ACD
TL288CJG	TL3474CD	TLC071IP	TLC2201ACP

Multisim 14.1 Base Edition Components

TLC2201AID	TLC2202ID	TLC2262MFK	TLC2274MN
TLC2201AIP	TLC2202IP	TLC2262MJG	TLC251ACD
TLC2201BCD	TLC2202MD	TLC2262MU	TLC251ACP
TLC2201BCP	TLC2202MFK	TLC2264CD	TLC251BCD
TLC2201BID	TLC2202MJG	TLC2264CN	TLC251BCP
TLC2201BIP	TLC2202MP	TLC2264CPW	TLC251CD
TLC2201CD	TLC2202Y	TLC2264CPWLE	TLC251CP
TLC2201CP	TLC2252AID	TLC2264MFK	TLC251Y
TLC2201ID	TLC2252AIP	TLC2264MJ	TLC252ACD
TLC2201IP	TLC2252AIPWLE	TLC2264MW	TLC252ACP
TLC2201MD	TLC2252CD	TLC2272ACD	TLC252ACPW
TLC2201MFK	TLC2252CP	TLC2272ACP	TLC252BCD
TLC2201MJG	TLC2252CPWLE	TLC2272CD	TLC252BCP
TLC2201MP	TLC2252MFK	TLC2272CP	TLC252BCPW
TLC2201Y	TLC2252MJG	TLC2272CPWLE	TLC252CD
TLC2202ACD	TLC2252MU	TLC2272Y	TLC252CP
TLC2202ACP	TLC2254CD	TLC2274ACD	TLC252CPW
TLC2202AID	TLC2254CN	TLC2274ACN	TLC254ACD
TLC2202AIP	TLC2254CPWLE	TLC2274ACPW	TLC254ACN
TLC2202BCD	TLC2254MFK	TLC2274CD	TLC254BCD
TLC2202BCP	TLC2254MJ	TLC2274CN	TLC254BCN
TLC2202BID	TLC2254MW	TLC2274CPWLE	TLC254CD
TLC2202BIP	TLC2262CD	TLC2274MD	TLC254CN
TLC2202CD	TLC2262CP	TLC2274MFK	TLC254CPW
TLC2202CP	TLC2262CPWLE	TLC2274MJ	TLC25L2ACD

Multisim 14.1 Base Edition Components

TLC25L2ACP	TLC2652AMFK	TLC2654AI-14D	TLC2654MN
TLC25L2BCD	TLC2652AMJ	TLC2654AID	TLC2654MP
TLC25L2BCP	TLC2652AMJG	TLC2654AIN	TLC271ACD
TLC25L2CD	TLC2652AMN	TLC2654AIP	TLC271ACP
TLC25L2CP	TLC2652AMP	TLC2654AM-14D	TLC271AID
TLC25L4CD	TLC2652C-14D	TLC2654AM-8D	TLC271AIP
TLC25L4CN	TLC2652C-8D	TLC2654AMF	TLC271BCD
TLC25M2ACD	TLC2652CN	TLC2654AMFK	TLC271BCP
TLC25M2ACP	TLC2652CP	TLC2654AMJ	TLC271BID
TLC25M2BCD	TLC2652I-14D	TLC2654AMJG	TLC271BIP
TLC25M2BCP	TLC2652ID	TLC2654AMN	TLC271CD
TLC25M2CD	TLC2652IN	TLC2654AMP	TLC271CP
TLC25M2CP	TLC2652IP	TLC2654C-14D	TLC271ID
TLC25M4CD	TLC2652M-14D	TLC2654C-8D	TLC271IP
TLC25M4CN	TLC2652M-8D	TLC2654CN	TLC271MD
TLC2652AC-14D	TLC2652MFK	TLC2654CP	TLC271MFK
TLC2652AC-8D	TLC2652MJ	TLC2654I-14D	TLC271MJG
TLC2652ACN	TLC2652MJG	TLC2654I-8D	TLC271MP
TLC2652ACP	TLC2652MN	TLC2654IN	TLC272CD
TLC2652AI-14D	TLC2652MP	TLC2654IP	TLC272CP
TLC2652AI-8D	TLC2652Y	TLC2654M-14D	TLC272CPW
TLC2652AIN	TLC2654AC-14D	TLC2654M-8D	TLC272ID
TLC2652AIP	TLC2654AC-8D	TLC2654MFK	TLC272IP
TLC2652AM-14D	TLC2654ACN	TLC2654MJ	TLC272MD
TLC2652AM-8D	TLC2654ACP	TLC2654MJG	TLC272MFK

Multisim 14.1 Base Edition Components

TLC272MJG	TLC279MJ	TLC27L4BIN	TLC27M2ACD
TLC272MP	TLC279MN	TLC27L4CD	TLC27M2ACP
TLC274CD	TLC27L2ACD	TLC27L4CN	TLC27M2AID
TLC274CN	TLC27L2ACP	TLC27L4ID	TLC27M2AIP
TLC274CPW	TLC27L2AID	TLC27L4IN	TLC27M2BCD
TLC274ID	TLC27L2AIP	TLC27L4MD	TLC27M2BCP
TLC274IN	TLC27L2BCD	TLC27L4MFK	TLC27M2BID
TLC274MD	TLC27L2BCP	TLC27L4MJ	TLC27M2BIP
TLC274MFK	TLC27L2BID	TLC27L4MN	TLC27M2CD
TLC274MJ	TLC27L2BIP	TLC27L7CD	TLC27M2CP
TLC274MN	TLC27L2CD	TLC27L7CP	TLC27M2ID
TLC277CD	TLC27L2CP	TLC27L7ID	TLC27M2IP
TLC277CP	TLC27L2ID	TLC27L7IP	TLC27M2MD
TLC277ID	TLC27L2IP	TLC27L7MD	TLC27M2MFK
TLC277IP	TLC27L2MD	TLC27L7MFK	TLC27M2MJG
TLC277MD	TLC27L2MFK	TLC27L7MJG	TLC27M2MP
TLC277MFK	TLC27L2MJG	TLC27L7MP	TLC27M4ACD
TLC277MJG	TLC27L2MP	TLC27L9CD	TLC27M4ACN
TLC277MP	TLC27L4ACD	TLC27L9CN	TLC27M4AID
TLC279CD	TLC27L4ACN	TLC27L9ID	TLC27M4AIN
TLC279CN	TLC27L4AID	TLC27L9IN	TLC27M4BCD
TLC279ID	TLC27L4AIN	TLC27L9MD	TLC27M4BCN
TLC279IN	TLC27L4BCD	TLC27L9MFK	TLC27M4BID
TLC279MD	TLC27L4BCN	TLC27L9MJ	TLC27M4BIN
TLC279MFK	TLC27L4BID	TLC27L9MP	TLC27M4CD

Multisim 14.1 Base Edition Components

TLC27M4CN	TLC339ID	TLC3702QJG	TLC374MD
TLC27M4ID	TLC339IN	TLC3704CD	TLC374MFK
TLC27M4IN	TLC339MD	TLC3704CN	TLC374MJ
TLC27M4MD	TLC339MN	TLC3704CPW	TLC374MN
TLC27M4MFK	TLC339QD	TLC3704ID	TLC374QD
TLC27M4MJ	TLC339QN	TLC3704IN	TLC374QN
TLC27M4MN	TLC352CD	TLC3704MFK	TLC393CD
TLC27M7CD	TLC352CP	TLC3704MJ	TLC393CP
TLC27M7CP	TLC352ID	TLC3704QJ	TLC393ID
TLC27M7ID	TLC352IP	TLC372CD	TLC393IP
TLC27M7IP	TLC352MFK	TLC372CP	TLC393MD
TLC27M7MD	TLC352MJG	TLC372CPW	TLC393MFK
TLC27M7MFK	TLC354CD	TLC372ID	TLC393MJG
TLC27M7MJG	TLC354CN	TLC372IP	TLC393MP
TLC27M7MP	TLC354CPW	TLC372MD	TLC551CD
TLC27M9CD	TLC354ID	TLC372MFK	TLC551CP
TLC27M9CN	TLC354IN	TLC372MJG	TLC552CD
TLC27M9ID	TLC354MD	TLC372MP	TLC552CN
TLC27M9IN	TLC354MN	TLC372QD	TLC555CD
TLC27M9MD	TLC3702CD	TLC372QP	TLC555CP
TLC27M9MFK	TLC3702CP	TLC374CD	TLC555CPSR
TLC27M9MJ	TLC3702ID	TLC374CN	TLC555CPW
TLC27M9MN	TLC3702IP	TLC374CPW	TLC555ID
TLC339CD	TLC3702MFK	TLC374ID	TLC555IP
TLC339CN	TLC3702MJG	TLC374IN	TLC555QDR

Multisim 14.1 Base Edition Components

TLC556CD	TLE2022ACD	TLE2024BIDW	TLE2027ID
TLC556CN	TLE2022ACP	TLE2024BIN	TLE2027IP
TLC556ID	TLE2022AID	TLE2024BMDW	TLE2027MD
TLC556IN	TLE2022AIP	TLE2024BMJ	TLE2027MFK
TLE2021ACD	TLE2022BCD	TLE2024BMN	TLE2027MJG
TLE2021ACP	TLE2022BCP	TLE2024CDW	TLE2027ML
TLE2021AID	TLE2022BID	TLE2024CN	TLE2027MP
TLE2021AIP	TLE2022BIP	TLE2024IDW	TLE2037ACD
TLE2021AMD	TLE2022CD	TLE2024IN	TLE2037ACP
TLE2021AMFK	TLE2022CDBLE	TLE2024MDW	TLE2037AID
TLE2021AMJG	TLE2022CP	TLE2024MFK	TLE2037AIP
TLE2021AMP	TLE2022CPWLE	TLE2024MJ	TLE2037AMD
TLE2021BI	TLE2022ID	TLE2024MN	TLE2037AMFK
TLE2021BMJG	TLE2022IP	TLE2024Y	TLE2037AMJG
TLE2021CD	TLE2022Y	TLE2027ACD	TLE2037AML
TLE2021CDBLE	TLE2024ACDW	TLE2027ACP	TLE2037AMP
TLE2021CP	TLE2024ACN	TLE2027AID	TLE2037CD
TLE2021CPWLE	TLE2024AIDW	TLE2027AIP	TLE2037CP
TLE2021ID	TLE2024AIN	TLE2027AMD	TLE2037ID
TLE2021IP	TLE2024AMDW	TLE2027AMFK	TLE2037IP
TLE2021MD	TLE2024AMFK	TLE2027AMJG	TLE2037MD
TLE2021MFK	TLE2024AMJ	TLE2027AML	TLE2037MFK
TLE2021MJG	TLE2024AMN	TLE2027AMP	TLE2037MJG
TLE2021MP	TLE2024BCDW	TLE2027CD	TLE2037ML
TLE2021Y	TLE2024BCN	TLE2027CP	TLE2037MP

Multisim 14.1 Base Edition Components

TLE2061ACD	TLE2061MD	TLE2062IP	TLE2064MN
TLE2061ACL	TLE2061MFK	TLE2062MD	TLE2064Y
TLE2061ACP	TLE2061MJG	TLE2062MFK	TLE2071CD
TLE2061AID	TLE2061ML	TLE2062MJG	TLE2071CP
TLE2061AIL	TLE2061MP	TLE2062MP	TLE2071MFK
TLE2061AIP	TLE2061Y	TLE2062Y	TLE2071MJG
TLE2061AMD	TLE2062ACD	TLE2064ACD	TLE2072CD
TLE2061AMFK	TLE2062ACP	TLE2064ACN	TLE2072CP
TLE2061AMJG	TLE2062AID	TLE2064AID	TLE2072MFK
TLE2061AML	TLE2062AIP	TLE2064AIN	TLE2074CN
TLE2061AMP	TLE2062AMD	TLE2064AMD	TLE2081CD
TLE2061BCL	TLE2062AMFK	TLE2064AMFK	TLE2081CP
TLE2061BIL	TLE2062AMJG	TLE2064AMJ	TLE2081MFK
TLE2061BIP	TLE2062AMP	TLE2064AMN	TLE2081MJG
TLE2061BMJG	TLE2062BCD	TLE2064BCN	TLE2082ACD
TLE2061BML	TLE2062BCP	TLE2064BIN	TLE2082ACP
TLE2061BMP	TLE2062BID	TLE2064BMJ	TLE2082AID
TLE2061CD	TLE2062BIP	TLE2064BMN	TLE2082AIP
TLE2061CDBLE	TLE2062BMD	TLE2064CD	TLE2082AMD
TLE2061CL	TLE2062BMFK	TLE2064CN	TLE2082AMFK
TLE2061CP	TLE2062BMJG	TLE2064ID	TLE2082AMJG
TLE2061CPWLE	TLE2062BMP	TLE2064IN	TLE2082AMP
TLE2061ID	TLE2062CD	TLE2064MD	TLE2082CD
TLE2061IL	TLE2062CP	TLE2064MFK	TLE2082CP
TLE2061IP	TLE2062ID	TLE2064MJ	TLE2082ID

Multisim 14.1 Base Edition Components

TLE2082IP	TLE2142AID	TLE2144MFK	TLE2161ML
TLE2082MD	TLE2142AIP	TLE2144MJ	TLE2161MP
TLE2082MFK	TLE2142AMD	TLE2144MN	TLE2227ACP
TLE2082MJG	TLE2142AMFK	TLE2144Y	TLE2227CDW
TLE2082MP	TLE2142AMJG	TLE2161ACD	TLE2227CP
TLE2084CN	TLE2142AMP	TLE2161ACP	TLE2237ACP
TLE2141ACD	TLE2142CD	TLE2161AID	TLE2237CDW
TLE2141ACP	TLE2142CP	TLE2161AIP	TLE2237CP
TLE2141AID	TLE2142ID	TLE2161AMD	TLE2425CD
TLE2141AIP	TLE2142IP	TLE2161AMFK	TLE2425ID
TLE2141AMD	TLE2142MD	TLE2161AMJG	TLE2426CD
TLE2141AMFK	TLE2142MFK	TLE2161AML	TLE2426IP
TLE2141AMJG	TLE2142MJG	TLE2161AMP	TL-OP
TLE2141AMP	TLE2142MP	TLE2161BCP	TL-OP1
TLE2141CD	TLE2142Y	TLE2161BIP	TLV1701AIDBVT
TLE2141CP	TLE2144ACN	TLE2161BMJ	TLV1701AIDCKT
TLE2141ID	TLE2144AIN	TLE2161BML	TLV1701AIDRLT
TLE2141IP	TLE2144AMFK	TLE2161BMP	TLV171IDBVT
TLE2141MD	TLE2144AMJ	TLE2161CD	TLV171IDR
TLE2141MFK	TLE2144AMN	TLE2161CP	TLV2211CDBV
TLE2141MJG	TLE2144CDW	TLE2161ID	TLV2211IDBV
TLE2141MP	TLE2144CN	TLE2161IP	TLV2221CDBV
TLE2141Y	TLE2144IDW	TLE2161MD	TLV2221IDBV
TLE2142ACD	TLE2144IN	TLE2161MFK	TLV2231CDBV
TLE2142ACP	TLE2144MDW	TLE2161MJG	TLV2231IDBV

Multisim 14.1 Base Edition Components

TLV2252ID	TLV2322IP	TLV2354IPW	TLV2375IN
TLV2252IP	TLV2322IPWLE	TLV2354MJ	TLV2375IPW
TLV2252MFK	TLV2324ID	TLV2361CDBV	TLV2401CD
TLV2252MJG	TLV2324IN	TLV2361IDBV	TLV2401CDBV
TLV2252MU	TLV2324IPWLE	TLV2362ID	TLV2401ID
TLV2254AID	TLV2332ID	TLV2362IDGK	TLV2401IDBV
TLV2254AIN	TLV2332IP	TLV2362IP	TLV2401IP
TLV2254AIPWLE	TLV2332IPWLE	TLV2362IPS	TLV2402CD
TLV2254ID	TLV2334ID	TLV2362IPW	TLV2402CDGK
TLV2254IN	TLV2334IN	TLV2370ID	TLV2402ID
TLV2254MFK	TLV2334IPWLE	TLV2370IDBV	TLV2402IDGK
TLV2254MJ	TLV2341ID	TLV2370IP	TLV2402IP
TLV2254QD	TLV2341IP	TLV2371ID	TLV2432AID
TLV2262AIPWLE	TLV2341IPWLE	TLV2371IDBV	TLV2432AIPW
TLV2262ID	TLV2342ID	TLV2371IP	TLV2432AMJG
TLV2262IP	TLV2342IP	TLV2372ID	TLV2434AID
TLV2262MFK	TLV2342IPWLE	TLV2372IDGK	TLV2434AIPW
TLV2262MJG	TLV2344ID	TLV2372IP	TLV2442CD
TLV2262MU	TLV2344IN	TLV2373ID	TLV2442CPW
TLV2264AIPWLE	TLV2344IPWLE	TLV2373IDGS	TLV2442MJG
TLV2264ID	TLV2352ID	TLV2373IN	TLV2444CD
TLV2264IN	TLV2352IP	TLV2374ID	TLV2444CPW
TLV2264MJ	TLV2352IPW	TLV2374IN	TLV2444ID
TLV2264QD	TLV2354ID	TLV2374IPW	TLV2444IPW
TLV2322ID	TLV2354IN	TLV2375ID	TLV2450AID

Multisim 14.1 Base Edition Components

TLV2450AIP	TLV2473AID	TLV2760IP	TLV3012AIDBVR
TLV2451AID	TLV2473AIP	TLV2761ID	TLV3012AIDCKR
TLV2451AIP	TLV2474AID	TLV2761IDBV	TLV313IDBVT
TLV2452AID	TLV2474AIN	TLV2761IP	TLV313IDCKT
TLV2452AIP	TLV2474AIPWP	TLV2762ID	TLV314IDBVT
TLV2453AID	TLV2475AID	TLV2762IDGK	TLV314IDCKT
TLV2453AIN	TLV2475AIN	TLV2762IP	TLV316IDBVT
TLV2454AID	TLV2475AIPWP	TLV2763ID	TLV316IDCKT
TLV2454AIN	TLV271CD	TLV2763IDGS	TLV3201AIDBVR
TLV2454AIPW	TLV271CDBVR	TLV2763IN	TLV3201AIDCKR
TLV2455AID	TLV271ID	TLV2764ID	TLV3202AID
TLV2455AIN	TLV271IDBVR	TLV2764IN	TLV3202AIDGK
TLV2455AIPW	TLV271IP	TLV2764IPW	TLV333IDBVT
TLV2460CD	TLV272CD	TLV2765ID	TLV333IDCKT
TLV2460CDBV	TLV272CDGK	TLV2765IN	TLV333IDR
TLV2460CP	TLV272ID	TLV2765IPW	TLV3401CD
TLV2461CD	TLV272IDGK	TLV2772CD	TLV3401CDBVR
TLV2461CDBV	TLV272IP	TLV2772CDGK	TLV3401ID
TLV2461CP	TLV274CD	TLV2772CP	TLV3401IDBVR
TLV2470AID	TLV274CPW	TLV2782AID	TLV3401IDG4
TLV2470AIP	TLV274ID	TLV2783AID	TLV3401IP
TLV2471AID	TLV274IN	TLV2784AID	TLV342ID
TLV2471AIP	TLV274IPW	TLV2784AIPW	TLV342IDGKR
TLV2472AID	TLV2760ID	TLV2785AID	TLV342IRUGR
TLV2472AIP	TLV2760IDBV	TLV2785AIPW	TLV3492AID

Multisim 14.1 Base Edition Components

TLV3492AIDCNT	TLV4113CDGQR	TLV73333PDQNR	TN4036
TLV3494AID	TLV4113ID	TMP90C800F	TOSHIBA-MIPS-HDR
TLV3494AIPWT	TLV4113IDGQ	TMP90C800N	TPS2811_SO8
TLV3501AID	TLV4113IN	TMP90C801F	TPS2812_SO8
TLV3501AIDBVR	TLV521DCKT	TMP90C801N	TPS2813_SO8
TLV3691IDCKR	TLV522DGKT	TMP94CM40F	TPS2814_SO8
TLV3691IDPFR	TLV6001IDBVT	TMS320C6711B-100GFNA	TPS2815_SO8
TLV3701CD	TLV6001IDCKT	TMS320LC2402A-PAG(64)	TPS2816_SOT23_5
TLV3701CDBVR	TLV70711PDQNR	TMS320LC2402A-PG(64)	TPS2817_SOT23_5
TLV3701ID	TLV70717DQNR	TMS320LC2402A-PZ(100)	TPS2818_SOT23_5
TLV3701IDBVR	TLV707335DQNR	TMS320LC2404A-PZ(100)	TPS2819_SOT23_5
TLV3701IP	TLV7111830DSER	TMS320LC2406A-PZ(100)	TPS2828_SOT23_5
TLV4110ID	TLV73310PDBVR	TMS320LC2406A-PZ(100)	TPS2829_SOT23_5
TLV4110IDGNR	TLV73310PDQNR	TMS320LF2402A-PG(64)	TPS2830_SO14
TLV4110IP	TLV73311PDBVR	TMS320LF2402A-PG(64)	TPS2831_SO14
TLV4111CD	TLV73311PDQNR	TMS320LF2403A-PAG(64)	TPS2832_SO8
TLV4111CDGN	TLV73312PDBVR	TMS320LF2406A-PZ(100)	TPS2833_SO8
TLV4111ID	TLV73312PDQNR	TMS320LF2407A-PGE(144)	TPS2834_SO14
TLV4111IDGN	TLV73315PDBVR	TN2219	TPS2835_SO14
TLV4112CD	TLV73315PDQNR	TN2219A	TPS2836_SO8
TLV4112CDGN	TLV73318PDBVR	TN2905	TPS2837_SO8
TLV4112CP	TLV73318PDQNR	TN2905A	TPS2838_SO16
TLV4112ID	TLV73325PDBVR		TPS2839_SO16
TLV4112IDGN	TLV73325PDQNR		TPS2848_SO14
TLV4112IP	TLV73333PDBVR		TPS2849_SO14

Multisim 14.1 Base Edition Components

TPS3780ADBVR	TPS70925DBVR	TPS71750DSER	TPS76701QD
TPS3780BDBVR	TPS70925DRVR	TPS72711YFFR	TPS76701QPWPR
TPS3780CDBVR	TPS70950DBVR	TPS72715DSET	TPS76715QD
TPS3780DDBVR	TPS70950DRVR	TPS72715YFFT	TPS76715QPWP
TPS3803-01DCKR	TPS715A33DRBT	TPS727185YFFR	TPS76718QD
TPS3839G25DBZR	TPS715A33DRVT	TPS72718DSET	TPS76718QPWP
TPS5300_SO32	TPS71701DCKR	TPS72718YFFT	TPS76725QD
TPS60240_SO8	TPS71709DSER	TPS72725DSET	TPS76725QPWP
TPS60241_SO8	TPS71710DCKR	TPS72727DSET	TPS76727QD
TPS60242_SO8	TPS71710DRVR	TPS727285DSER	TPS76727QPWP
TPS60243_SO8	TPS71711DCKR	TPS72728DSET	TPS76728QD
TPS70612DBVR	TPS71712DCKR	TPS72728YFFT	TPS76730QD
TPS70612DRVR	TPS71713DCKR	TPS73530QDRBRQ1	TPS76730QPWP
TPS70615DBVR	TPS71715DCKR	TPS75701KC	TPS76733QD
TPS70615DRVR	TPS71719DCKR	TPS75701KTTT	TPS76733QPWP
TPS70618DBVR	TPS71721DCKR	TPS76301DBVR	TPS76750QD
TPS70618DRVR	TPS71726DCKR	TPS76316DBVR	TPS76750QPWP
TPS70625DBVR	TPS71727DCKR	TPS76318DBVR	TPS76801QD
TPS70625DRVR	TPS71727DSER	TPS76325DBVR	TPS76801QPWP
TPS70628DBVR	TPS717285DCKR	TPS76327DBVR	TPS76815QD
TPS70628DRVR	TPS71729DCKR	TPS76328DBVR	TPS76815QPWP
TPS70630DBVR	TPS71730DCKR	TPS76330DBVR	TPS76818QD
TPS70630DRVR	TPS71733DCKR	TPS76333DBVR	TPS76818QPWP
TPS70633DBVR	TPS71733DRVR	TPS76338DBVR	TPS76825QD
TPS70633DRVR	TPS71733DSER	TPS76350DBVR	TPS76825QPWP

Multisim 14.1 Base Edition Components

TPS76827QD	TPS79718DCKR	TPSMC33A-E3/51T	TRIANGULAR_VOLTAGE
TPS76828QD	TPS797285DCKR	TPSMC36A/9AT	TRIODE_VIRTUAL
TPS76830QD	TPS79730DCKR	TPSMC39A-E3/57T	TRISTATE
TPS76830QPWP	TPS79733DCKR	TPSMP18AHM3/84A	TRISTATE_NEG
TPS76833QD	TPS799L54YZYR	TPSMP24AHM3/84A	TS_VIRTUAL
TPS76833QPWP	TPS7A4901DGNR	TPSMP27AHE3/84A	TS5A3357DCUR
TPS76850QD	TPS7A4901DRBR	TPSMP30AHM3/84A	TS5A3359DCUR
TPS76850QPWP	TPS7A7300RGWR	TPSMP36AHM3/84A	TS5A3359YZPR
TPS77618QPWPRQ1	TPS7A8300RGRR	TRANSFER_FUNCTION_BLOCK	TVP5145PFP-TQFP(80)
TPS78618DCQR	TPS7A8300RGWR	TRANSISTOR	TVS3V3L4U
TPS78618KTTT	TPSMA16AHE3/61T	TRANSISTOR_DELAY	U257
TPS78625DCQR	TPSMA20A/11T	TRANSISTOR_DIODE	U308
TPS78625KTTT	TPSMA27AHE3/61T	TRANSISTOR_DIODE_DELAY	U309
TPS78628DCQR	TPSMA30AHE3/61T	TRANSPORT_DELAY	U310
TPS78628KTTT	TPSMA33AHE3/61T	TRF37A75IDSGR	U401
TPS78630DCQR	TPSMA36AHE3/5AT	TRF37B75IDSGR	U402
TPS78630KTTT	TPSMB24AHE3/52T	TRF37C75IDSGR	U403
TPS78633DCQR	TPSMB27A/2	TRIAC	U404
TPS78633KTTT	TPSMB30AHE3/52T	TRIANGULAR_CURRENT	U405
TPS79301DBVR	TPSMB33AHE3/52T		U406
TPS79516DCQR	TPSMB36A/5T		U440
TPS79518DCQR	TPSMB39A-E3/2T		U441
TPS79525DCQR	TPSMC22A-E3/57T		UA709AMJ
TPS79533DCQR	TPSMC27A-E3/57T		UA709AMJG
	TPSMC30AHE3_A/H		

Multisim 14.1 Base Edition Components

UA709AMU	UA748CP	UC3842A_DIP8	UCC27324_SO8
UA709AMW	UA748JG	UC3842A_SO8	UCC27325_SO8
UA709CD	UA748MJG	UC3842B_DIP8	UCC37323_SO8
UA709CJG	UA748MU	UC3842B_SO8	UCC37324_SO8
UA709CP	UC1705_DIP8	UC3842T_DIP8	UCC37325_SO8
UA709MJ	UC2705_DIP8	UC3842T_SO8	UF4002-E3/54
UA709MU	UC2842A_DIP8	UC3843A_DIP8	UF4007-E3/54
UA709MW	UC2842A_SO8	UC3843A_SO8	UF5406-E3/54
UA723CD	UC2842B_DIP8	UC3843B_DIP8	UG06D-E3/54
UA723CFK	UC2842B_SO8	UC3843B_SO8	UG1D-E3/54
UA723CJ	UC2843A_DIP8	UC3843T_DIP8	UG30DPT-E3/45
UA723CN	UC2843A_SO8	UC3843T_SO8	UG5JT-E3/45
UA723MU	UC2843B_DIP8	UC3844A_DIP8	UG8DT-E3/45
UA741CD	UC2843B_SO8	UC3844A_SO8	UG8JCT-E3/45
UA741CP	UC2844A_DIP8	UC3844B_DIP8	UG8JT-E3/45
UA741MFK	UC2844A_SO8	UC3844B_SO8	ULN2001_DIP16
UA741MJ	UC2844B_DIP8	UC3844T_DIP8	ULN2001_SO16
UA741MJG	UC2844B_SO8	UC3844T_SO8	ULN2002_DIP16
UA741MU	UC2845A_DIP8	UC3845A_DIP8	ULN2002_SO16
UA747CD	UC2845A_SO8	UC3845A_SO8	ULN2003_DIP16
UA747CN	UC2845B_DIP8	UC3845B_DIP8	ULN2003_SO16
UA747MFK	UC2845B_SO8	UC3845B_SO8	ULN2004_DIP16
UA747MJ	UC3248	UC3845T_DIP8	ULN2004_SO16
UA747MW	UC3705_DIP8	UC3845T_SO8	UNDCD_BARGRAPH
UA748CD	UC3842	UCC27323_SO8	US1G-E3/61T

Multisim 14.1 Base Edition Components

US1J-E3/5AT	VBPW34S	VO2611-X017T	VOLTAGE_CONTROLLED_CURRENT_SOURCE
US1M-E3/61T	VBPW34SR	VO2630	
UX60-MB-5ST	VCC	VO2630-X006	VOLTAGE_CONTROLLED_DPDT
V_REF1	VDAC	VO2630-X007T	
V_REF2	VDAC16	VO2631	VOLTAGE_CONTROLLED_INDUCTOR_VIRTUAL
V_REF3	VDD	VO2631-X006	
V_REF4	VEE	VO2631-X007T	VOLTAGE_CONTROLLED_LIMITER
V_REF5	VN10LF	VO2631-X017T	
V10P10-M3/86A	VO0600T	VO4661	VOLTAGE_CONTROLLED_PIECEWISE_LINEAR_SOURCE
V12P10-M3/86A	VO0601T	VO4661-X006	
V8P10HM3/86A	VO0601-X001T	VO4661-X007T	VOLTAGE_CONTROLLED_RESISTOR_VIRTUAL
VARIABLE_CAPACITOR	VO0611T	VO615A-3	
	VO0630T	VO615A-3X001	VOLTAGE_CONTROLLED_SINE_WAVE
VARIABLE_CAPACITOR_VIRTUAL	VO0631T	VO615A-3X006	
	VO0631-X001T	VO615A-3X007T	VOLTAGE_CONTROLLED_SPDT
VARIABLE_INDUCTOR	VO0661T	VO615A-3X008T	
	VO2601	VO615A-3X009T	VOLTAGE_CONTROLLED_SPST
VARIABLE_INDUCTOR_VIRTUAL	VO2601-X006	VO615A-3X016	
VARIABLE_PULLUP_VIRTUAL	VO2601-X007T	VO615A-3X017T	VOLTAGE_CONTROLLED_SPST_ANIMATED
	VO2601-X016	VO615A-3X018T	
VARIABLE_RESISTOR_VIRTUAL	VO2601-X017T	VO615A-3X019T	VOLTAGE_CONTROLLED_SQUARE_WAVE
VBP104FAS	VO2611	VOLTAGE_CONTROLLED_CAPACITOR_VIRTUAL	
VBP104FASR	VO2611-X006		VOLTAGE_CONTROLLED_TRIANGLE_WAVE
VBPW34FAS	VO2611-X007T		
VBPW34FASR	VO2611-X016		

Multisim 14.1 Base Edition Components

VOLTAGE_CONTROLLED_VOLTAGE_SOURCE	XC3020A-PQ100	XC5202-5PQ100C	XC5206-5PC84C
	XC3030A-PQ100	XC5202-5TQ144C	XC5206-5PQ100C
VOLTAGE_DIFFERENTIATOR	XC3030A-VQ100	XC5202-5VQ64C	XC5206-5TQ144C
	XC3030L-VQ100	XC5202-6PC84C	XC5206-6PC84C
VOLTAGE_GAIN_BLOCK	XC3042A-PQ100	XC5202-6PQ100C	XC5206-6PQ100C
	XC3042A-VQ100	XC5202-6TQ144C	XC5206-6TQ144C
VOLTAGE_HYSTESIS_BLOCK	XC3042L-VQ100	XC5202-6VQ64C	XC5210-3PC84C
VOLTAGE_INTEGRATOR	XC3120A-PQ100	XC5204-3PC84C	XC5210-3TQ144C
	XC3130A-PQ100	XC5204-3PQ100C	XC5210-4PC84C
VOLTAGE_LIMITER	XC3130A-VQ100	XC5204-3TQ144C	XC5210-4TQ144C
VOLTAGE_SLEW_RATE_BLOCK	XC3142A-PQ100	XC5204-4PC84C	XC5210-5PC84C
	XC3142A-VQ100	XC5204-4PQ100C	XC5210-5TQ144C
VOLTAGE_SUMMER	XC3142L-VQ100	XC5204-4TQ144C	XC5210-6PC84C
VOLTMETER_H	XC4002XL-1PC84C	XC5204-5PC84C	XC5210-6TQ144C
VOLTMETER_HR	XC4002XL-2PC84C	XC5204-5PQ100C	XC5215-3PQ160C
VOLTMETER_V	XC4002XL-3PC84C	XC5204-5TQ144C	XC5215-4PQ160C
VOLTMETER_VR	XC5202-3PC84C	XC5204-6PC84C	XC5215-5PQ160C
VOM452T	XC5202-3PQ100C	XC5204-6PQ100C	XC5215-6PQ160C
VOM453T	XC5202-3TQ144C	XC5204-6TQ144C	XC9572XL-10TQ100C
VSKY20301608-G4-08	XC5202-3VQ64C	XC5206-3PC84C	XC9572XL-7TQ100C
VSKY20401608-G4-08	XC5202-4PC84C	XC5206-3PQ100C	XC505-3PC84C
	XC5202-4PQ100C	XC5206-3TQ144C	XC505-4PC84C
VSS	XC5202-4TQ144C	XC5206-4PC84C	XC505XL-4PC84C
W06G-E4/51	XC5202-4VQ64C	XC5206-4PQ100C	XC510-3PC84C
WOBBLE_STICK	XC5202-5PC84C	XC5206-4TQ144C	

Multisim 14.1 Base Edition Components

XCS10-4PC84C	XNOR8	Z4KE140	Z84C10-DIP(40)
XCS10XL-4PC84C	XNOR8	Z4KE140A	Z84C10-PLCC(44)
XCS20-3VQ100C	XOR2	Z4KE150	Z84C15-QFP(100)
XCS20-4VQ100C	XOR2	Z4KE150A	Z84C15-VQFP(100)
XCS20XL-4VQ100C	XOR3	Z4KE160	Z84C20-DIP(40)
XCS30-3VQ100C	XOR3	Z4KE160A	Z84C20-PLCC(44)
XCS30-4VQ100C	XOR4	Z4KE170	Z84C30-DIP(28)
XCS30XL-4VQ100C	XOR4	Z4KE170A	Z84C30-PLCC(44)
XCS40-4PQ208C	XOR5	Z4KE180	Z84C30-QFP(44)
XCS40XL-4PQ208C	XOR5	Z4KE180A	Z84C40-DIP(40)
XILINX-PARALLEL- III-IV-HDR	XOR6	Z4KE190	Z84C41-DIP(40)
	XOR6	Z4KE190A	Z84C42-DIP(40)
XILINX-PARALLEL- IV-HDR	XOR7	Z4KE200	Z84C43-QFP(44)
	XOR7	Z4KE200A	Z84C44-PLCC(44)
XNOR2	XOR8	Z80180-DIP(64)	Z84C90-LQFP(100)
XNOR2	XOR8	Z80180-PLCC(68)	Z84C90-PLCC(84)
XNOR3	Z08470-DIP(40)	Z80180-QFP(80)	Z8L180-DIP(64)
XNOR4	Z4KE100	Z80181-QFP(100)	Z8L180-PLCC(68)
XNOR4	Z4KE100A	Z80182-QFP(100)	Z8L180-QFP(80)
XNOR5	Z4KE110	Z80182-VQFP(100)	Z8L182-QFP(100)
XNOR5	Z4KE110A	Z80195-QFP(100)	Z8L182-VQFP(100)
XNOR6	Z4KE120	Z84015-QFP(100)	Z8S180-DIP(64)
XNOR6	Z4KE120A	Z84C00-DIP(40)	Z8S180-PLCC(68)
XNOR7	Z4KE130	Z84C00-PLCC(44)	Z8S180-QFP(80)
XNOR7	Z4KE130A	Z84C00-QFP(44)	ZC820

Multisim 14.1 Base Edition Components

ZC821	ZGL41_180	ZPD6.8	ZTX239
ZC822	ZGL41_190	ZPD7.5	ZTX239B
ZC823	ZGL41_200	ZPD8.2	ZTX320
ZC824	ZPD10	ZTX1047A	ZTX321
ZC825	ZPD11	ZTX1048A	ZTX325
ZC826	ZPD12	ZTX1049A	ZTX327
ZC830A	ZPD13	ZTX1051A	ZTX337A
ZC831A	ZPD15	ZTX1053A	ZTX338A
ZC832A	ZPD16	ZTX1055A	ZTX360
ZC833A	ZPD18	ZTX107	ZTX450
ZC834A	ZPD2.7	ZTX107B	ZTX454
ZC835A	ZPD20	ZTX108	ZTX455
ZC836A	ZPD22	ZTX108B	ZTX458
ZDX1F	ZPD24	ZTX109	ZTX549
ZDX2F	ZPD27	ZTX109B	ZTX550
ZDX5	ZPD3.0	ZTX212	ZTX558
ZENER	ZPD3.3	ZTX212A	ZTX601B
ZGL41_100	ZPD3.6	ZTX213	ZTX604
ZGL41_110	ZPD3.9	ZTX213A	ZTX605
ZGL41_120	ZPD30	ZTX214	ZTX614
ZGL41_130	ZPD33	ZTX214A	ZTX618
ZGL41_140	ZPD4.3	ZTX237	ZTX649
ZGL41_150	ZPD4.7	ZTX237B	ZTX650
ZGL41_160	ZPD5.1	ZTX238	ZTX651
ZGL41_170	ZPD6.2	ZTX238B	ZTX653

Multisim 14.1 Base Edition Components

ZTX657	ZTX851
ZTX658	ZTX869
ZTX688B	ZTX948
ZTX689B	ZTX949
ZTX690B	ZTX951
ZTX692B	ZTX953
ZTX694B	ZTX955
ZTX696B	ZTX956
ZTX704	ZTX957
ZTX705	ZTX958
ZTX718	ZTX968
ZTX749	ZVN0124A
ZTX750	ZVN2106A
ZTX751	ZVN2106G
ZTX753	ZVN3306A
ZTX757	ZVN3306F
ZTX758	ZVN3310F
ZTX788A	ZVN4210G
ZTX788B	ZVN4306G
ZTX789A	ZVN4310G
ZTX790A	ZVN4424G
ZTX792A	ZVP2106A
ZTX795A	ZVP2106G
ZTX796A	ZVP3306
ZTX849	ZVP4424A