

Multisim 14.0 Base Components

741	685119136923	1 mF	1 mF
1028	0.5_AMP	[T510X108M004AT E023]	[T520Y108M2R5AT E025]
1294	02BZ2.2	1 mF	1 mF
2462	02DZ4.7	[T513E108M004AH 6110]	[T530X108M003AT E010]
2466	05AZ2.2	1 mF	1 mF
2468	1 mF	[T513X108M004AH 6110]	[T530X108M004AT E006]
2477	[T491E108M004AT]		
2481	1 mF	1 mF	1 mF
284258	[T491X108M004AT]	[T513X108M004AH 6120]	[T530X108M2R5AT E005]
1708026	1 mF	1 mF	1 mF
1708039	[T494E108M004AT]	[T520D108M2R5AT E015]	[T530X108M2R5AT E006]
1708042	1 mF	1 mF	1 mF
1708055	[T495E108M004AT E035]	[T520D108M2R5AT E030]	[T530Y108M2R5AT E005]
1708084	1 mF	1 mF	1 nF
1708110	[T495E108M006AT E050]	[T520X108M003AT E015]	[C0402C102K1HACT U]
1786837			
1786866	1 mF	1 mF	1 nF
1786918	[T495X108M004AT E070]	[T520X108M003AT E030]	[C0402C102K3GACT U]
1786963	1 mF	1 mF	1 nF
1787205	[T510E108M004AT E010]	[T520X108M2R5AT E010]	[C0402C102K3HACT U]
1787234	1 mF	1 mF	1 nF
1787289	[T510E108M004AT E018]	[T520Y108M2R5AT E010]	[C0402C102K3RACT U]
1787331	1 mF	1 mF	1 nF
1787386	[T510X108M004AT E018]	[T520Y108M2R5AT E015]	[C0402C102K4RACT U]
1787580			

Multisim 14.0 Base Components

1 nF [C0402C102K5HACT U]	1 nF [C0603C102K4RACT U]	1 nF [C0805C102K4RACT U]	1 nF [C1206C102K5GACT U]
1 nF [C0402C102K5RACT U]	1 nF [C0603C102K5GACT U]	1 nF [C0805C102K5GACT U]	1 nF [C1206C102K5RACT U]
1 nF [C0402C102K8RACT U]	1 nF [C0603C102K5HACT U]	1 nF [C0805C102K5RACT U]	1 nF [C1206C102KCGAC TU]
1 nF [C0402C102K9RACT U]	1 nF [C0603C102K5RACT U]	1 nF [C0805C102K8RACT U]	1 nF [C1210C102K1GACT U]
1 nF [C0603C102K1HACT U]	1 nF [C0603C102K8RACT U]	1 nF [C0805C102KARACT U]	1 nF [C1210C102K2GACT U]
1 nF [C0603C102K1RACT U]	1 nF [C0603C102K9RACT U]	1 nF [C1206C102K1GACT U]	1 nF [C1210C102K5GACT U]
1 nF [C0603C102K2RACT U]	1 nF [C0805C102K1GACT U]	1 nF [C1206C102K1RACT U]	1 nF [C1210C102KBGAC TU]
1 nF [C0603C102K3GACT U]	1 nF [C0805C102K1RACT U]	1 nF [C1206C102K2GACT U]	1 nF [C1210C102KCGAC TU]
1 nF [C0603C102K3HACT U]	1 nF [C0805C102K2RACT U]	1 nF [C1206C102K2RACT U]	1 nF [C1210C102KDGAC TU]
1 nF [C0603C102K3RACT U]	1 nF [C0805C102K3GACT U]	1 nF [C1206C102K3RACT U]	1 nF [C1812C102K1GACT U]
1 nF [C0603C102K4GACT U]	1 nF [C0805C102K3RACT U]	1 nF [C1206C102K4RACT U]	1 nF [C1812C102K2GACT U]

Multisim 14.0 Base Components

1 nF [C1812C102K5GACT U]	1 uF [C0402C105K8PACT U]	1 uF [C0805C105K4RACT U]	1 uF [C1206C105K3RACT U]
1 nF [C1812C102KBGAC TU]	1 uF [C0402C105K9PACT U]	1 uF [C0805C105K8NAC TU]	1 uF [C1206C105K4RACT U]
1 nF [C1812C102KCGAC TU]	1 uF [C0603C105K3PACT U]	1 uF [C0805C105K8PACT U]	1 uF [C1206C105K5RACT U]
1 nF [C1812C102KDGAC TU]	1 uF [C0603C105K4PACT U]	1 uF [C0805C105K8RACT U]	1 uF [C1206C105K8RACT U]
1 nF [C1825C102KBGAC TU]	1 uF [C0603C105K4RACT U]	1 uF [C0805C105K9PACT U]	1 uF [C1206C105K9RACT U]
1 nF [C2220C102KBGAC TU]	1 uF [C0603C105K8PACT U]	1 uF [C0805C105K9RACT U]	1 uF [C1206C105M3VAC TU]
1 nF [C2225C102KBGAC TU]	1 uF [C0603C105K8RACT U]	1 uF [C0805C105M3VAC TU]	1 uF [C1206C105M4VAC TU]
1 nF [CA064C102K3RACT U]	1 uF [C0603C105K9PACT U]	1 uF [C0805C105M4VAC TU]	1 uF [C1206C105M8VAC TU]
1 nF [CA064C102K4RACT U]	1 uF [C0603C105K9RACT U]	1 uF [C0805C105M8VAC TU]	1 uF [C1206F105K4RACT U]
1 nF [CA064C102K5RACT U]	1 uF [C0805C105K3PACT U]	1 uF [C1206C105K3NAC TU]	1 uF [C1210C105K1RACT U]
1 nF [CA064C102K8RACT U]	1 uF [C0805C105K4PACT U]	1 uF [C1206C105K3PACT U]	1 uF [C1210C105K3PACT U]

Multisim 14.0 Base Components

1 uF [C1210C105K3RACT U]	1 uF [C1210F105K3RACT U]	1 uF [C1825C105M5UAC TU]	1 uF [T491A105M025AT]
1 uF [C1210C105K4PACT U]	1 uF [C1210F105K4RACT U]	1 uF [C2220C105K5R1C7 186]	1 uF [T491A105M035AT]
1 uF [C1210C105K4RACT U]	1 uF [C1812C105K3RACT U]	1 uF [C2220C105K5RACT U]	1 uF [T491B105M025AT]
1 uF [C1210C105K5NAC TU]	1 uF [C1812C105K5RACT U]	1 uF [C2220C105KARACT U]	1 uF [T491B105M050AT]
1 uF [C1210C105K5PACT U]	1 uF [C1812C105M5UAC TU]	1 uF [C2225C105K1RACT U]	1 uF [T491C105M050AT]
1 uF [C1210C105K5RACT U]	1 uF [C1812F105K1RACT U]	1 uF [C2225C105K5RACT U]	1 uF [T491V105M050AT]
1 uF [C1210C105K8RACT U]	1 uF [C1812F105K3RACT U]	1 uF [C2225C105KARACT U]	1 uF [T494A105M016AT]
1 uF [C1210C105K9RACT U]	1 uF [C1812F105K5RACT U]	1 uF [C2225C105M5UAC TU]	1 uF [T494A105M020AT]
1 uF [C1210C105M3VAC TU]	1 uF [C1825C105K2RACT U]	1 uF [T409C105M025AH 4250]	1 uF [T494A105M035AT]
1 uF [C1210C105M5UAC TU]	1 uF [C1825C105K5RACT U]	1 uF [T489A105M025AT E6K6]	1 uF [T494B105M025AT]
1 uF [C1210C105M8VAC TU]	1 uF [C1825C105KARACT U]	1 uF [T491A105M016AT]	1 uF [T494B105M035AT]
		1 uF [T491A105M020AT]	1 uF [T494B105M050AT]

Multisim 14.0 Base Components

1 uF [T494C105M050AT]	1.1 nF [C0603C112K1HACT U]	1.2 nF [C0402C122K4RACT U]	1.2 nF [C0805C122K1RACT U]
1 uF [T494S105M020AT]	1.1 nF [C0603C112K3HACT U]	1.2 nF [C0402C122K5HACT U]	1.2 nF [C0805C122K2RACT U]
1 uF [T494V105M050AT]	1.1 nF [C0603C112K5HACT U]	1.2 nF [C0402C122K5RACT U]	1.2 nF [C0805C122K3GACT U]
1 uF [T495A105M020AT E3K0]	1.1 nF [C1210C112KBGAC TU]	1.2 nF [C0603C122K1HACT U]	1.2 nF [C0805C122K4RACT U]
1 uF [T495B105M035AT E1K7]	1.1 nF [C1812C112KBGAC TU]	1.2 nF [C0603C122K1RACT U]	1.2 nF [C0805C122K5GACT U]
1 uF [T497A105M015AT 6110]	1.1 nF [C1825C112KBGAC TU]	1.2 nF [C0603C122K3HACT U]	1.2 nF [C0805C122K5RACT U]
1 uF [T498A105M016AT E6K5]	1.1 nF [C2220C112KBGAC TU]	1.2 nF [C0603C122K3RACT U]	1.2 nF [C0805C122KARACT U]
1 uF [T498A105M020AT E5K9]	1.1 nF [C2225C112KBGAC TU]	1.2 nF [C0603C122K4RACT U]	1.2 nF [C1206C122K1GACT U]
1 uF [T498A105M035AT E10K]	1.1 nF [CDR33BP112BKSM]	1.2 nF [C0603C122K5HACT U]	1.2 nF [C1206C122K1RACT U]
1.1 nF [C0402C112K3HACT U]	1.2 nF [C0402C122K3HACT U]	1.2 nF [C0603C122K5RACT U]	1.2 nF [C1206C122K2GACT U]
1.1 nF [C0402C112K5HACT U]	1.2 nF [C0402C122K3RACT U]	1.2 nF [C0805C122K1GACT U]	1.2 nF [C1206C122K2RACT U]

Multisim 14.0 Base Components

1.2 nF [C1206C122K5GACT U]	1.2 uF [C0805C125K9PACT U]	1.2 uF [C2225C125KARACT U]	1.5 mF [T530X158M003AT E008]
1.2 nF [C1206C122K5RACT U]	1.2 uF [C0805C125K9RACT U]	1.3 nF [C0402C132K3HACT U]	1.5 mF [T530X158M2R5AT E005]
1.2 nF [C1210C122KBGAC TU]	1.2 uF [C1206C125K3RACT U]	1.3 nF [C0402C132K5HACT U]	1.5 nF [C0402C152K3HACT U]
1.2 nF [C1812C122KBGAC TU]	1.2 uF [C1206C125K4RACT U]	1.3 nF [C0603C132K1HACT U]	1.5 nF [C0402C152K3RACT U]
1.2 nF [C1825C122KBGAC TU]	1.2 uF [C1206C125K8RACT U]	1.3 nF [C0603C132K3HACT U]	1.5 nF [C0402C152K4RACT U]
1.2 nF [C2220C122KBGAC TU]	1.2 uF [C1210C125K3PACT U]	1.3 nF [C0603C132K5HACT U]	1.5 nF [C0402C152K5HACT U]
1.2 nF [C2225C122KBGAC TU]	1.2 uF [C1210C125K3RACT U]	1.3 nF [C1210C132KBGAC TU]	1.5 nF [C0402C152K5RACT U]
1.2 uF [C0805C125K4PACT U]	1.2 uF [C1210F125K4RACT U]	1.3 nF [C1812C132KBGAC TU]	1.5 nF [C0402C152K8RACT U]
1.2 uF [C0805C125K4RACT U]	1.2 uF [C1825C125K5RACT U]	1.3 nF [C1825C132KBGAC TU]	1.5 nF [C0603C152K1HACT U]
1.2 uF [C0805C125K8PACT U]	1.2 uF [C1825C125M5UAC TU]	1.3 nF [C2220C132KBGAC TU]	1.5 nF [C0603C152K1RACT U]
1.2 uF [C0805C125K8RACT U]	1.2 uF [C2220C125K5RACT U]	1.3 nF [C2225C132KBGAC TU]	1.5 nF [C0603C152K2RACT U]

Multisim 14.0 Base Components

1.5 nF [C0603C152K3HACT U]	1.5 nF [C0805C152K4RACT U]	1.5 nF [C1210C152K5GACT U]	1.5 uF [C0805C155K8RACT U]
1.5 nF [C0603C152K3RACT U]	1.5 nF [C0805C152K5GACT U]	1.5 nF [C1210C152KBGAC TU]	1.5 uF [C0805C155K9PACT U]
1.5 nF [C0603C152K4RACT U]	1.5 nF [C0805C152K5RACT U]	1.5 nF [C1812C152K2GACT U]	1.5 uF [C0805C155K9RACT U]
1.5 nF [C0603C152K5HACT U]	1.5 nF [C0805C152KARACT U]	1.5 nF [C1812C152KBGAC TU]	1.5 uF [C1206C155K3RACT U]
1.5 nF [C0603C152K5RACT U]	1.5 nF [C1206C152K1GACT U]	1.5 nF [C1825C152KBGAC TU]	1.5 uF [C1206C155K4PACT U]
1.5 nF [C0603C152K8RACT U]	1.5 nF [C1206C152K1RACT U]	1.5 nF [C2220C152KBGAC TU]	1.5 uF [C1206C155K4RACT U]
1.5 nF [C0805C152K1GACT U]	1.5 nF [C1206C152K2GACT U]	1.5 nF [C2225C152KBGAC TU]	1.5 uF [C1206C155K8PACT U]
1.5 nF [C0805C152K1RACT U]	1.5 nF [C1206C152K2RACT U]	1.5 nF [CDR04BP152BKSM]	1.5 uF [C1206C155K8RACT U]
1.5 nF [C0805C152K2RACT U]	1.5 nF [C1206C152K5GACT U]	1.5 uF [C0805C155K4PACT U]	1.5 uF [C1206C155K9RACT U]
1.5 nF [C0805C152K3RACT U]	1.5 nF [C1206C152K5RACT U]	1.5 uF [C0805C155K4RACT U]	1.5 uF [C1210C155K3PACT U]
1.5 nF [C0805C152K4GACT U]	1.5 nF [C1210C152K1GACT U]	1.5 uF [C0805C155K8PACT U]	1.5 uF [C1210C155K3RACT U]

Multisim 14.0 Base Components

1.5 uF [C1210C155K4RACT U]	1.5 uF [T491A155M025AT]	1.5 uF [T494S155M020AT]	1.5KE91A-E3/54
1.5 uF [C1210F155K4RACT U]	1.5 uF [T491B155M025AT]	1.5 uF [T498C155M035AT E3K3]	1.5KE91ARL4G
1.5 uF [C1825C155K5RACT U]	1.5 uF [T491B155M035AT]	1.5KE100A-E3/54	1.5SMC12AT3G
1.5 uF [C1825C155M5UAC TU]	1.5 uF [T491C155M035AT]	1.5KE100CA-E3/54	1.5SMC13A-E3/57T
1.5 uF [C1825C155M5UAC TU]	1.5 uF [T491C155M050AT]	1.5KE110CA-E3/54	1.5SMC15AT3G
1.5 uF [C2220C155K5RACT U]	1.5 uF [T491D155M050AT]	1.5KE12A-E3/54	1.5SMC15CA-E3/57T
1.5 uF [C2225C155K5RACT U]	1.5 uF [T491S155M020AT]	1.5KE12CA-E3/54	1.5SMC180A-E3/57T
1.5 uF [C2225C155K5RACT U]	1.5 uF [T494A155M010AT]	1.5KE12CA-E3/54	1.5SMC18AT3G
1.5 uF [C2225C155M5UAC TU]	1.5 uF [T494A155M016AT]	1.5KE130CA-E3/54	1.5SMC18CA-E3/57T
1.5 uF [C2225C155M5UAC TU]	1.5 uF [T494A155M025AT]	1.5KE160CA-E3/54	1.5SMC20AT3G
1.5 uF [T419A155M015AH 4250]	1.5 uF [T494B155M025AT]	1.5KE180A-E3/54	1.5SMC24AT3G
1.5 uF [T489C155M050AT E1K5]	1.5 uF [T494B155M035AT]	1.5KE18A-E3/54	1.5SMC33AT3G
1.5 uF [T491A155M010AT]	1.5 uF [T494C155M035AT]	1.5KE200A-E3/54	1.5SMC39A-E3/57T
1.5 uF [T491A155M016AT]	1.5 uF [T494C155M050AT]	1.5KE200CA-E3/54	1.5SMC39AT3G
1.5 uF [T491A155M020AT]	1.5 uF [T494D155M050AT]	1.5KE20A-E3/51	1.5SMC39AT3G
		1.5KE36A-E3/54	1.5SMC43AT3G
		1.5KE36CA-E3/54	1.5SMC540A-E3/57T
		1.5KE39ARL4G	1.5SMC6.8A/57T
		1.5KE39CA-E3/54	1.5SMC6.8AT3G
		1.5KE47A-E3/54	1.5SMC6.8CA-E3/57T
		1.5KE47AG	1.5SMC62AT3G
		1.5KE47ARL4G	1.5SMC75CA-E3/57T
		1.5KE51CA-E3/54	
		1.5KE75ARL4G	

Multisim 14.0 Base Components

1.5SMC91AT3G	1.8 nF	1.8 nF	1.8 nF
1.6 nF	[C0402C182K5RACT	[C0805C182K5GACT	[C1210C182KBGAC
[C0603C162K1HACT	U]	U]	TU]
U]	1.8 nF	1.8 nF	1.8 nF
1.6 nF	[C0603C182K1HACT	[C0805C182K5RACT	[C1812C182KBGAC
[C0603C162K3HACT	U]	U]	TU]
U]	1.8 nF	1.8 nF	1.8 nF
1.6 nF	[C0603C182K1RACT	[C0805C182KARACT	[C1825C182KBGAC
[C0603C162K5HACT	U]	U]	TU]
U]	1.8 nF	1.8 nF	1.8 nF
1.6 nF	[C0603C182K3HACT	[C1206C182K1GACT	[C2220C182KBGAC
[C0805C162K4GACT	U]	U]	TU]
U]	1.8 nF	1.8 nF	1.8 nF
1.6 nF	[C0603C182K3RACT	[C1206C182K1RACT	[C2225C182KBGAC
[C1206C162K5GACT	U]	U]	TU]
U]	1.8 nF	1.8 nF	1.8 uF
1.6 nF	[C0603C182K5HACT	[C1206C182K2GACT	[C0805C185K4PACT
[C1210C162KBGAC	U]	U]	U]
TU]	1.8 nF	1.8 nF	1.8 uF
1.6 nF	[C0603C182K5RACT	[C1206C182K5GACT	[C0805C185K4RACT
[C1812C162KBGAC	U]	U]	U]
TU]	1.8 nF	1.8 nF	1.8 uF
1.6 nF	[C0805C182K1GACT	[C1206C182K5RACT	[C0805C185K8PACT
[C1825C162KBGAC	U]	U]	U]
TU]	1.8 nF	1.8 nF	1.8 uF
1.6 nF	[C0805C182K1RACT	[C1210C182K1GACT	[C0805C185K8RACT
[C2220C162KBGAC	U]	U]	U]
TU]	1.8 nF	1.8 nF	1.8 uF
1.6 nF	[C0805C182K2RACT	[C1210C182K2GACT	[C0805C185K9PACT
[C2225C162KBGAC	U]	U]	U]
TU]	1.8 nF	1.8 nF	1.8 uF
1.8 nF	[C0805C182K4RACT	[C1210C182K5GACT	[C0805C185K9RACT
[C0402C182K3RACT	U]	U]	U]
U]			

Multisim 14.0 Base Components

1.8 uF [C1206C185K3PACT U]	10 nF [C0201C103K8PACT U]	10 nF [C0603C103K3RACT U]	10 nF [C0805C103K4RACT U]
1.8 uF [C1206C185K4RACT U]	10 nF [C0201C103K9PACT U]	10 nF [C0603C103K4RACT U]	10 nF [C0805C103K5GACT U]
1.8 uF [C1206C185K8RACT U]	10 nF [C0402C103K3RACT U]	10 nF [C0603C103K5RACT U]	10 nF [C0805C103K5HACT U]
1.8 uF [C1210C185K3PACT U]	10 nF [C0402C103K4RACT U]	10 nF [C0603C103K8RACT U]	10 nF [C0805C103K5RACT U]
1.8 uF [C1210C185K3RACT U]	10 nF [C0402C103K5RACT U]	10 nF [C0603C103K9RACT U]	10 nF [C0805C103K8RACT U]
1.8 uF [C1210F185K4RACT U]	10 nF [C0402C103K8RACT U]	10 nF [C0805C103K1GACT U]	10 nF [C0805C103KARACT U]
1.8 uF [C1825C185K5RACT U]	10 nF [C0402C103K9RACT U]	10 nF [C0805C103K1HACT U]	10 nF [C0805C103M1UAC TU]
1.8 uF [C2220C185K5RACT U]	10 nF [C0603C103K1RACT U]	10 nF [C0805C103K1RACT U]	10 nF [C0805C103M5UAC TU]
1.8 uF [C2225C185K5RACT U]	10 nF [C0603C103K2RACT U]	10 nF [C0805C103K3GACT U]	10 nF [C0805F103K1RACT U]
1.8 uF [C2225C185M5UAC TU]	10 nF [C0603C103K3GACT U]	10 nF [C0805C103K3HACT U]	10 nF [C0805F103K2RACT U]
1_AMP 10 nF [C0201C103K4PACT U]	10 nF [C0603C103K3HACT U]	10 nF [C0805C103K3RACT U]	10 nF [C0805F103K3RACT U]

Multisim 14.0 Base Components

10 nF [C0805F103K4RACT U]	10 nF [C1206C103K5RACT U]	10 nF [C1812C103K2RACT U]	10 nF [CA064C103K4RACT U]
10 nF [C0805F103K5RACT U]	10 nF [C1206C103KARACT U]	10 nF [C1812C103K5GACT U]	10 nF [CA064C103K5RACT U]
10 nF [C1206C103K1HACT U]	10 nF [C1206C103M1UAC TU]	10 nF [C1812C103K5RACT U]	10 nF [CA064C103K8RACT U]
10 nF [C1206C103K1RACT U]	10 nF [C1206C103M5UAC TU]	10 nF [C1825C103K1GACT U]	10 pF [C0402C100K3GACT U]
10 nF [C1206C103K2RACT U]	10 nF [C1210C103K1RACT U]	10 nF [C1825C103K2GACT U]	10 pF [C0402C100K4GACT U]
10 nF [C1206C103K3GACT U]	10 nF [C1210C103K2RACT U]	10 nF [C1825C103K5GACT U]	10 pF [C0402C100K5GACT U]
10 nF [C1206C103K3HACT U]	10 nF [C1210C103K5GACT U]	10 nF [C2220C103K1GACT U]	10 pF [C0402C100K8GACT U]
10 nF [C1206C103K3RACT U]	10 nF [C1210C103K5RACT U]	10 nF [C2220C103K2GACT U]	10 pF [C0603C100K1GACT U]
10 nF [C1206C103K4GACT U]	10 nF [C1210C103KARACT U]	10 nF [C2225C103K2GACT U]	10 pF [C0603C100K2GACT U]
10 nF [C1206C103K4RACT U]	10 nF [C1812C103K1GACT U]	10 nF [C2225C103KCGAC TU]	10 pF [C0603C100K3GACT U]
10 nF [C1206C103K5HACT U]	10 nF [C1812C103K1RACT U]	10 nF [CA064C103K3RACT U]	10 pF [C0603C100K5GACT U]

Multisim 14.0 Base Components

10 pF [C0805C100K1GACT U]	10 pF [C1210C100K5GACT U]	10 uF [A700V106M12RAT E060]	10 uF [C1206C106K9RACT U]
10 pF [C0805C100K2GACT U]	10 pF [C1210C100KBGAC TU]	10 uF [C0805C106K4PACT U]	10 uF [C1206C106M8VAC TU]
10 pF [C0805C100K5GACT U]	10 pF [C1812C100KBGAC TU]	10 uF [C0805C106K8PACT U]	10 uF [C1206C106M9VAC TU]
10 pF [C0805C100KBGAC TU]	10 pF [C1825C100KBGAC TU]	10 uF [C0805C106K9PACT U]	10 uF [C1210C106K3PACT U]
10 pF [C0805C100KDGAC TU]	10 pF [C2220C100KBGAC TU]	10 uF [C0805C106M9VAC TU]	10 uF [C1210C106K3RACT U]
10 pF [C0805H100K5GAC TU]	10 pF [C2225C100KBGAC TU]	10 uF [C1206C106K3PACT U]	10 uF [C1210C106K4PACT U]
10 pF [C1206C100K1GACT U]	10 pF [CA064C100K1GAC TU]	10 uF [C1206C106K4PACT U]	10 uF [C1210C106K4RACT U]
10 pF [C1206C100K2GACT U]	10 pF [CA064C100K2GAC TU]	10 uF [C1206C106K4RACT U]	10 uF [C1210C106K8NAC TU]
10 pF [C1206C100K5GACT U]	10 pF [CA064C100K4GAC TU]	10 uF [C1206C106K8PACT U]	10 uF [C1210C106K8PACT U]
10 pF [C1206C100KBGAC TU]	10 pF [CA064C100K5GAC TU]	10 uF [C1206C106K8RACT U]	10 uF [C1210C106K8RACT U]
10 pF [C1210C100K2GACT U]	10 uF [A700V106M016AT E045]	10 uF [C1206C106K9PACT U]	10 uF [C1210C106K9PACT U]

Multisim 14.0 Base Components

10 uF [C1210C106K9RACT U]	10 uF [T491B106M010AT]	10 uF [T491T106M006AT]	10 uF [T494B106M006AT]
10 uF [C1210C106M4VAC TU]	10 uF [T491B106M016AT]	10 uF [T491T106M010AT]	10 uF [T494B106M010AT]
10 uF [C1210C106M8VAC TU]	10 uF [T491B106M020AT]	10 uF [T491T106M016AT]	10 uF [T494B106M016AT]
10 uF [C1210C106M9VAC TU]	10 uF [T491C106M010AT]	10 uF [T491U106M016AT]	10 uF [T494B106M020AT]
10 uF [T429E106M020AH 4250]	10 uF [T491C106M016AT]	10 uF [T491U106M020AT]	10 uF [T494C106M010AT]
10 uF [T429H106M035AH 4250]	10 uF [T491C106M020AT]	10 uF [T491V106M035AT]	10 uF [T494C106M016AT]
10 uF [T491A106M004AT]	10 uF [T491C106M025AT]	10 uF [T491X106M050AT]	10 uF [T494C106M020AT]
10 uF [T491A106M006AT]	10 uF [T491D106M035AT]	10 uF [T493C106M020AH 6110]	10 uF [T494C106M025AT]
10 uF [T491A106M010AT]	10 uF [T491D106M025AT]	10 uF [T494A106M004AT]	10 uF [T494C106M035AT]
10 uF [T491A106M016AT]	10 uF [T491D106M035AT]	10 uF [T494A106M006AT]	10 uF [T494D106M025AT]
10 uF [T491A106M020AT]	10 uF [T491D106M050AT]	10 uF [T494A106M010AT]	10 uF [T494D106M035AT]
10 uF [T491B106M004AT]	10 uF [T491S106M004AT]	10 uF [T494A106M016AT]	10 uF [T494D106M050AT]
10 uF [T491B106M006AT]	10 uF [T491S106M006AT]	10 uF [T494A106M020AT]	10 uF [T494S106M004AT]
	10 uF [T491S106M010AT]	10 uF [T494B106M004AT]	10 uF [T494S106M006AT]

Multisim 14.0 Base Components

10 uF [T494S106M010AT]	10 uF [T495C106M025AT E275]	10 uF [T496D106M025AT 6110]	10 uF [T510X106M050AT E120]
10 uF [T494T106M006AT]	10 uF [T495C106M025AT E450]	10 uF [T497F106M015AT 6110]	10 uF [T520A106M010AT E080]
10 uF [T494T106M010AT]	10 uF [T495D106M035AT E125]	10 uF [T498B106M006AT E2K1]	10 uF [T520B106M016AT E100]
10 uF [T494U106M016AT]	10 uF [T495D106M035AT E250]	10 uF [T498B106M010AT E1K8]	10 uF [T521D106M050AT E090]
10 uF [T494U106M020AT]	10 uF [T495D106M035AT E300]	10 uF [T498B106M016AT E2K8]	10 uF [T521X106M063AT E050]
10 uF [T494V106M035AT]	10 uF [T495T106M016AT E4K0]	10 uF [T498C106M016AT E1K4]	10 uF [T541X106M063AH 6510]
10 uF [T494X106M050AT]	10 uF [T495X106M035AT E200]	10 uF [T498C106M020AT E1K1]	10_AMP
10 uF [T495A106M010AT E1K8]	10 uF [T495X106M035AT E250]	10 uF [T498C106M025AT E1K1]	100 nF [C0201C104K9PACT U]
10 uF [T495B106M010AT E750]	10 uF [T495X106M050AT E250]	10 uF [T498D106M035AT E700]	100 nF [C0402C104K4PACT U]
10 uF [T495B106M020AT E1K0]	10 uF [T495X106M050AT E260]	10 uF [T498D106M050AT E1K0]	100 nF [C0402C104K8PACT U]
10 uF [T495C106M020AT E400]	10 uF [T495X106M050AT E300]	10 uF [T510X106M050AT E090]	100 nF [C0402C104K8RACT U]
10 uF [T495C106M020AT E475]			

Multisim 14.0 Base Components

100 nF [C0402C104K9PACT U]	100 nF [C0805C104K3RACT U]	100 nF [C1206C104K3GACT U]	100 nF [C1206F104K4RACT U]
100 nF [C0402C104K9RACT U]	100 nF [C0805C104K4RACT U]	100 nF [C1206C104K3HACT U]	100 nF [C1206F104K5RACT U]
100 nF [C0603C104K3RACT U]	100 nF [C0805C104K5RACT U]	100 nF [C1206C104K3RACT U]	100 nF [C1210C104K1GACT U]
100 nF [C0603C104K4RACT U]	100 nF [C0805C104K8RACT U]	100 nF [C1206C104K4RACT U]	100 nF [C1210C104K1HACT U]
100 nF [C0603C104K5RACT U]	100 nF [C0805C104K9RACT U]	100 nF [C1206C104K5RACT U]	100 nF [C1210C104K1RACT U]
100 nF [C0603C104K8RACT U]	100 nF [C0805C104M3VAC TU]	100 nF [C1206C104KARACT U]	100 nF [C1210C104K2RACT U]
100 nF [C0603C104K9RACT U]	100 nF [C0805C104M4VAC TU]	100 nF [C1206C104M1UAC TU]	100 nF [C1210C104K3GACT U]
100 nF [C0603C104M3VAC TU]	100 nF [C0805C104M5UAC TU]	100 nF [C1206C104M5UAC TU]	100 nF [C1210C104K3HACT U]
100 nF [C0603C104M4VAC TU]	100 nF [C0805C104M5VAC TU]	100 nF [C1206F104K1RACT U]	100 nF [C1210C104K3RACT U]
100 nF [C0603C104M8VAC TU]	100 nF [C1206C104K1RACT U]	100 nF [C1206F104K2RACT U]	100 nF [C1210C104K4RACT U]
100 nF [C0805C104K1RACT U]	100 nF [C1206C104K2RACT U]	100 nF [C1206F104K3RACT U]	100 nF [C1210C104K5GACT U]

Multisim 14.0 Base Components

100 nF [C1210C104K5HACT U]	100 nF [C1812C104K1GACT U]	100 nF [C1812F104K3RACT U]	100 nF [CA064C104K8RACT U]
100 nF [C1210C104K5RACT U]	100 nF [C1812C104K1HACT U]	100 nF [C1812F104K5RACT U]	100 nF [T491A104M035AT]
100 nF [C1210C104K8RACT U]	100 nF [C1812C104K1R1C7 186]	100 nF [C1825C104K1RACT U]	100 nF [T491A104M050AT]
100 nF [C1210C104KARACT U]	100 nF [C1812C104K1RACT U]	100 nF [C1825C104K2RACT U]	100 nF [T494A104M050AT]
100 nF [C1210C104M1UAC TU]	100 nF [C1812C104K2RACT U]	100 nF [C2220C104K1GACT U]	100 pF [03028BR101AKZC]
100 nF [C1210C104M5UAC TU]	100 nF [C1812C104K5GACT U]	100 nF [C2220C104K2GACT U]	100 pF [C0201C101K3GACT U]
100 nF [C1210F104K1RACT U]	100 nF [C1812C104K5HACT U]	100 nF [C2220C104K5GACT U]	100 pF [C0402C101K1HACT U]
100 nF [C1210F104K2RACT U]	100 nF [C1812C104K5RACT U]	100 nF [C2225C104K1RACT U]	100 pF [C0402C101K3GACT U]
100 nF [C1210F104K3RACT U]	100 nF [C1812C104M1UAC TU]	100 nF [C2225C104K2RACT U]	100 pF [C0402C101K3HACT U]
100 nF [C1210F104K4RACT U]	100 nF [C1812F104K1RACT U]	100 nF [C2225C104K5RACT U]	100 pF [C0402C101K4GACT U]
100 nF [C1210F104K5RACT U]	100 nF [C1812F104K2RACT U]	100 nF [CA064C104K4RACT U]	100 pF [C0402C101K5GACT U]

Multisim 14.0 Base Components

100 pF [C0402C101K5HACT U]	100 pF [C0805C101K4GACT U]	100 pF [C1206C101KCGAC TU]	100 pF [C2220C101KBGAC TU]
100 pF [C0402C101K8GACT U]	100 pF [C0805C101K5GACT U]	100 pF [C1206C101KDGAC TU]	100 pF [C2225C101KBGAC TU]
100 pF [C0603C101K1GACT U]	100 pF [C0805C101KBGAC TU]	100 pF [C1206C101KGGAC TU]	100 pF [CA064C101K1GAC TU]
100 pF [C0603C101K3GACT U]	100 pF [C0805C101KCGAC TU]	100 pF [C1210C101K5GACT U]	100 pF [CA064C101K3GAC TU]
100 pF [C0603C101K4GACT U]	100 pF [C0805C101KDGAC TU]	100 pF [C1210C101KBGAC TU]	100 pF [CA064C101K5GAC TU]
100 pF [C0603C101K5GACT U]	100 pF [C0805H101K5GAC TU]	100 pF [C1210C101KCGAC TU]	100 pF [CA064C101K8GAC TU]
100 pF [C0603C101K5RACT U]	100 pF [C1206C101K1GACT U]	100 pF [C1210C101KDGAC TU]	100 uF [A700D107M006AT E015]
100 pF [C0603C101K8GACT U]	100 pF [C1206C101K2GACT U]	100 pF [C1812C101KBGAC TU]	100 uF [A700D107M006AT E018]
100 pF [C0805C101K1GACT U]	100 pF [C1206C101K3GACT U]	100 pF [C1812C101KDGAC TU]	100 uF [A700V107M002AT E018]
100 pF [C0805C101K2GACT U]	100 pF [C1206C101K5GACT U]	100 pF [C1812C101KHGAC TU]	100 uF [A700V107M002AT E025]
100 pF [C0805C101K3GACT U]	100 pF [C1206C101KBGAC TU]	100 pF [C1825C101KBGAC TU]	100 uF [A700V107M002AT E028]

Multisim 14.0 Base Components

100 uF [A700X107M008AT E010]	100 uF [T491C107M010AT]	100 uF [T491V107M016AT]	100 uF [T494E107M020AT]
100 uF [A700X107M008AT E015]	100 uF [T491D107M004AT]	100 uF [T491X107M016AT]	100 uF [T494T107M004AT]
100 uF [A700X107M010AT E010]	100 uF [T491D107M006AT]	100 uF [T491X107M020AT]	100 uF [T494T107M2R5AT]
100 uF [A700X107M010AT E015]	100 uF [T491D107M010AT]	100 uF [T491X107M025AT]	100 uF [T494U107M004AT]
100 uF [A700X107M010AT E015]	100 uF [T491D107M016AT]	100 uF [T494A107M004AT]	100 uF [T494U107M006AT]
100 uF [T489C107M010AT E500]	100 uF [T491D107M020AT]	100 uF [T494B107M004AT]	100 uF [T494V107M006AT]
100 uF [T489D107M010AT E150]	100 uF [T491E107M020AT]	100 uF [T494C107M004AT]	100 uF [T494V107M010AT]
100 uF [T489D107M010AT E440]	100 uF [T491T107M004AT]	100 uF [T494C107M006AT]	100 uF [T494V107M016AT]
100 uF [T491A107M004AT]	100 uF [T491T107M2R5AT]	100 uF [T494D107M004AT]	100 uF [T494X107M016AT]
100 uF [T491B107M004AT]	100 uF [T491U107M004AT]	100 uF [T494D107M006AT]	100 uF [T494X107M020AT]
100 uF [T491B107M006AT]	100 uF [T491U107M006AT]	100 uF [T494D107M010AT]	100 uF [T494X107M025AT]
100 uF [T491B107M010AT]	100 uF [T491V107M006AT]	100 uF [T494D107M016AT]	100 uF [T495B107M006AT E400]
100 uF [T491C107M004AT]	100 uF [T491V107M010AT]		100 uF [T495B107M006AT E700]
100 uF [T491C107M006AT]			

Multisim 14.0 Base Components

100 uF [T495B107M010AT E350]	100 uF [T495E107M020AT E200]	100 uF [T498D107M010AT E600]	100 uF [T520B107M004AT E035]
100 uF [T495C107M006AT E150]	100 uF [T495T107M2R5AT E3K0]	100 uF [T510E107M025AT E050]	100 uF [T520B107M004AT E040]
100 uF [T495D107M006AT E050]	100 uF [T495V107M006AT E150]	100 uF [T510X107M020AT E040]	100 uF [T520B107M004AT E070]
100 uF [T495D107M006AT E130]	100 uF [T495V107M010AT E100]	100 uF [T510X107M020AT E045]	100 uF [T520B107M006AT E015]
100 uF [T495D107M010AT E050]	100 uF [T495V107M010AT E150]	100 uF [T513D107M016AH 6110]	100 uF [T520B107M006AT E018]
100 uF [T495D107M010AT E065]	100 uF [T495X107M010AT E100]	100 uF [T513E107M025AH 6110]	100 uF [T520B107M006AT E025]
100 uF [T495D107M010AT E080]	100 uF [T495X107M016AT E080]	100 uF [T513X107M020AH 6110]	100 uF [T520B107M006AT E035]
100 uF [T495D107M010AT E100]	100 uF [T495X107M016AT E100]	100 uF [T513X107M020AH 6120]	100 uF [T520B107M006AT E040]
100 uF [T495D107M016AT E100]	100 uF [T495X107M020AT E100]	100 uF [T520B107M003AT E035]	100 uF [T520B107M006AT E070]
100 uF [T495D107M016AT E125]	100 uF [T495X107M020AT E150]	100 uF [T520B107M003AT E040]	100 uF [T520B107M2R5AT E035]
100 uF [T495E107M020AT E060]	100 uF [T498D107M006AT E600]	100 uF [T520B107M003AT E070]	100 uF [T520B107M2R5AT E040]

Multisim 14.0 Base Components

100 uF [T520C107M006AT E025]	100 uF [T520T107M2R5AT E070]	100 uF [T520W107M006AT E040]	100 uF [T540B107M004AH 6510]
100 uF [T520C107M006AT E045]	100 uF [T520U107M004AT E055]	100 uF [T520W107M010AT E040]	100 uF [T540D107M010AH 6510]
100 uF [T520C107M010AT E025]	100 uF [T520U107M006AT E055]	100 uF [T521D107M016AT E050]	10029449-001RLF 100V_100W
100 uF [T520C107M010AT E045]	100 uF [T520V107M006AT E007]	100 uF [T521V107M016AT E050]	10104111-0001LF 105081-0001
100 uF [T520D107M006AT E007]	100 uF [T520V107M006AT E009]	100 uF [T521X107M025AT E060]	10Line_Bussed 10Line_Isolated
100 uF [T520D107M010AT E018]	100 uF [T520V107M006AT E012]	100 uF [T525B107M003AT E080]	11 pF [C0805C110KBGAC TU]
100 uF [T520D107M010AT E055]	100 uF [T520V107M006AT E045]	100 uF [T525B107M004AT E080]	11 pF [C1206C110KBGAC TU]
100 uF [T520D107M010AT E080]	100 uF [T520V107M010AT E018]	100 uF [T525D107M010AT E025]	11 pF [C1210C110KBGAC TU]
100 uF [T520T107M004AT E070]	100 uF [T520V107M010AT E025]	100 uF [T525D107M010AT E055]	11 pF [C1812C110KBGAC TU]
100 uF [T520T107M004AT E150]	100 uF [T520V107M010AT E045]	100 uF [T525T107M2R5AT E080]	11 pF [C1825C110KBGAC TU]
100 uF [T520T107M006AT E070]	100 uF [T520V107M010AT E050]	100 uF [T528I107M003ATE 200]	11 pF [C2220C110KBGAC TU]

Multisim 14.0 Base Components

11 pF [C2225C110KBGAC TU]	110 pF [C2220C111KBGAC TU]	12 nF [C0603C123K5RACT U]	12 nF [C0805C123KARACT U]
110 pF [C0402C111K1HACT U]	110 pF [C2225C111KBGAC TU]	12 nF [C0805C123K1GACT U]	12 nF [C0805F123K1RACT U]
110 pF [C0402C111K3HACT U]	12 nF [C0402C123K4RACT U]	12 nF [C0805C123K1HACT U]	12 nF [C0805F123K3RACT U]
110 pF [C0402C111K5HACT U]	12 nF [C0402C123K5RACT U]	12 nF [C0805C123K1RACT U]	12 nF [C0805F123K4RACT U]
110 pF [C0603C111K5GACT U]	12 nF [C0402C123K8PACT U]	12 nF [C0805C123K3HACT U]	12 nF [C0805F123K5RACT U]
110 pF [C0805C111K1GACT U]	12 nF [C0402C123K8RACT U]	12 nF [C0805C123K3RACT U]	12 nF [C1206C123K1HACT U]
110 pF [C1206C111K5GACT U]	12 nF [C0402C123K9PACT U]	12 nF [C0805C123K4RACT U]	12 nF [C1206C123K1RACT U]
110 pF [C1206C111KBGAC TU]	12 nF [C0402C123K9RACT U]	12 nF [C0805C123K5GACT U]	12 nF [C1206C123K2RACT U]
110 pF [C1210C111KBGAC TU]	12 nF [C0603C123K1RACT U]	12 nF [C0805C123K5HACT U]	12 nF [C1206C123K3HACT U]
110 pF [C1812C111KBGAC TU]	12 nF [C0603C123K3RACT U]	12 nF [C0805C123K5RACT U]	12 nF [C1206C123K5HACT U]
110 pF [C1825C111KBGAC TU]	12 nF [C0603C123K4RACT U]	12 nF [C0805C123K8RACT U]	12 nF [C1206C123K5RACT U]

Multisim 14.0 Base Components

12 nF [C1206C123KARACT U]	12 pF [C0201C120K3GACT U]	12 pF [C1206C120K5GACT U]	120 nF [C0805C124K1RACT U]
12 nF [C1210C123K1GACT U]	12 pF [C0402C120K4GACT U]	12 pF [C1206C120KBGAC TU]	120 nF [C0805C124K3RACT U]
12 nF [C1210C123K1HACT U]	12 pF [C0402C120K5GACT U]	12 pF [C1210C120KBGAC TU]	120 nF [C0805C124K4RACT U]
12 nF [C1210C123K3HACT U]	12 pF [C0603C120K1GACT U]	12 pF [C1812C120KBGAC TU]	120 nF [C0805C124K5RACT U]
12 nF [C1210C123K4RACT U]	12 pF [C0603C120K2GACT U]	12 pF [C1825C120KBGAC TU]	120 nF [C0805C124K8RACT U]
12 nF [C1210C123K5GACT U]	12 pF [C0603C120K3GACT U]	12 pF [C2220C120KBGAC TU]	120 nF [C1206C124K1RACT U]
12 nF [C1210C123K5HACT U]	12 pF [C0603C120K5GACT U]	12 pF [C2225C120KBGAC TU]	120 nF [C1206C124K2RACT U]
12 nF [C1210C123K5RACT U]	12 pF [C0805C120K1GACT U]	12 pF [CA064C120K5GAC TU]	120 nF [C1206C124K3RACT U]
12 nF [C1210C123KARACT U]	12 pF [C0805C120K5GACT U]	12 uF [C1210C126K8PACT U]	120 nF [C1206C124K4RACT U]
12 nF [C1812C123K1RACT U]	12 pF [C0805C120KBGAC TU]	120 nF [C0603C124K4RACT U]	120 nF [C1206C124K5RACT U]
12 nF [C2220C123K2GACT U]	12 pF [C1206C120K1GACT U]	120 nF [C0603C124K8RACT U]	120 nF [C1206C124M5UAC TU]

Multisim 14.0 Base Components

120 nF [C1210C124K1RACT U]	120 nF [C1812C124K5GACT U]	120 pF [03029BR121AKZC]	120 pF [C1206C121K2GACT U]
120 nF [C1210C124K3HACT U]	120 nF [C1812C124K5HACT U]	120 pF [C0402C121K1HACT U]	120 pF [C1206C121K5GACT U]
120 nF [C1210C124K5HACT U]	120 nF [C1812C124K5RACT U]	120 pF [C0402C121K3HACT U]	120 pF [C1206C121KBGAC TU]
120 nF [C1210C124K5RACT U]	120 nF [C1812C124M1UAC TU]	120 pF [C0402C121K5GACT U]	120 pF [C1206C121KDGAC TU]
120 nF [C1210F124K1RACT U]	120 nF [C1812F124K1RACT U]	120 pF [C0402C121K5HACT U]	120 pF [C1210C121KBGAC TU]
120 nF [C1210F124K3RACT U]	120 nF [C1812F124K2RACT U]	120 pF [C0603C121K1GACT U]	120 pF [C1812C121KBGAC TU]
120 nF [C1210F124K4RACT U]	120 nF [C1812F124K3RACT U]	120 pF [C0603C121K5GACT U]	120 pF [C1825C121KBGAC TU]
120 nF [C1210F124K5RACT U]	120 nF [C1812F124K5RACT U]	120 pF [C0805C121K1GACT U]	120 pF [C2220C121KBGAC TU]
120 nF [C1812C124K1GACT U]	120 nF [C2220C124K1GACT U]	120 pF [C0805C121K2GACT U]	120 pF [C2225C121KBGAC TU]
120 nF [C1812C124K1HACT U]	120 nF [C2220C124K5GACT U]	120 pF [C0805C121K5GACT U]	120 pF [CA064C121K5GAC TU]
120 nF [C1812C124K2RACT U]	120 nF [C2225C124K1RACT U]	120 pF [C1206C121K1GACT U]	120 uF [A700D127M004AT E015]

Multisim 14.0 Base Components

120 uF [A700D127M004AT E018]	13 pF [C0603C130K2GACT U]	130 pF [C0402C131K3HACT U]	15 nF [C0402C153K8PACT U]
120 uF [A700D127M006AT E012]	13 pF [C0603C130K5GACT U]	130 pF [C0402C131K5HACT U]	15 nF [C0402C153K8RACT U]
120 uF [A700D127M006AT E015]	13 pF [C0805C130K5GACT U]	130 pF [C0805H131K3GAC TU]	15 nF [C0402C153K9PACT U]
120 uF [A700D127M006AT E018]	13 pF [C0805C130KBGAC TU]	130 pF [C1206C131KBGAC TU]	15 nF [C0402C153K9RACT U]
120 uF [A700V127M002AT E018]	13 pF [C1206C130KBGAC TU]	130 pF [C1210C131KBGAC TU]	15 nF [C0603C153K1RACT U]
120 uF [A700X127M010AT E010]	13 pF [C1210C130KBGAC TU]	130 pF [C1812C131KBGAC TU]	15 nF [C0603C153K3RACT U]
120 uF [A700X127M010AT E015]	13 pF [C1812C130KBGAC TU]	130 pF [C1825C131KBGAC TU]	15 nF [C0603C153K4RACT U]
120 uF [T520B127M006AT E035]	13 pF [C1825C130KBGAC TU]	130 pF [C2220C131KBGAC TU]	15 nF [C0603C153K5RACT U]
120V_100W 120V_250W	13 pF [C2220C130KBGAC TU]	130 pF [C2225C131KBGAC TU]	15 nF [C0805C153K1GACT U]
1-282834-0 12A02CH-TL-E 12A02MH-TL-E	13 pF [C2225C130KBGAC TU]	15 nF [C0402C153K4RACT U]	15 nF [C0805C153K1HACT U]
12V_10W 12V_25W	130 pF [C0402C131K1HACT U]	15 nF [C0402C153K5RACT U]	15 nF [C0805C153K1RACT U]

Multisim 14.0 Base Components

15 nF [C0805C153K3HACT U]	15 nF [C0805F153K4RACT U]	15 nF [C1210C153K1GACT U]	15 nF [C1812C153K2RACT U]
15 nF [C0805C153K3RACT U]	15 nF [C0805F153K5RACT U]	15 nF [C1210C153K1HACT U]	15 nF [C1812C153K5GACT U]
15 nF [C0805C153K4RACT U]	15 nF [C1206C153K1HACT U]	15 nF [C1210C153K1RACT U]	15 nF [C1812C153K5HACT U]
15 nF [C0805C153K5GACT U]	15 nF [C1206C153K1RACT U]	15 nF [C1210C153K2RACT U]	15 nF [C1812C153K5RACT U]
15 nF [C0805C153K5HACT U]	15 nF [C1206C153K2RACT U]	15 nF [C1210C153K3HACT U]	15 nF [C1825C153K5GACT U]
15 nF [C0805C153K5RACT U]	15 nF [C1206C153K3HACT U]	15 nF [C1210C153K5HACT U]	15 nF [C2220C153K2GACT U]
15 nF [C0805C153K8RACT U]	15 nF [C1206C153K4RACT U]	15 nF [C1210C153K5RACT U]	15 nF [C2225C153K5GACT U]
15 nF [C0805C153KARACT U]	15 nF [C1206C153K5HACT U]	15 nF [C1210C153KARACT U]	15 nF [CA064C153K5RACT U]
15 nF [C0805C153M5UAC TU]	15 nF [C1206C153K5RACT U]	15 nF [C1812C153K1GACT U]	15 pF [C0201C150K3GACT U]
15 nF [C0805F153K1RACT U]	15 nF [C1206C153KARACT U]	15 nF [C1812C153K1HACT U]	15 pF [C0402C150K3GACT U]
15 nF [C0805F153K3RACT U]	15 nF [C1206C153M5UAC TU]	15 nF [C1812C153K1RACT U]	15 pF [C0402C150K4GACT U]

Multisim 14.0 Base Components

15 pF [C0402C150K5GACT U]	15 pF [C0805C150KBGAC TU]	15 pF [CA064C150K4GAC TU]	15 uF [T429F156M010AH 4250]
15 pF [C0402C150K8GACT U]	15 pF [C1206C150K1GACT U]	15 pF [CA064C150K5GAC TU]	15 uF [T429F156M020AH 4250]
15 pF [C0603C150K1GACT U]	15 pF [C1206C150K2GACT U]	15 uF [A700V156M12RAT E040]	15 uF [T489D156M025AT E300]
15 pF [C0603C150K2GACT U]	15 pF [C1206C150K5GACT U]	15 uF [C1210C156K4PACT U]	15 uF [T491A156M004AT]
15 pF [C0603C150K4GACT U]	15 pF [C1206C150KBGAC TU]	15 uF [C1210C156K8PACT U]	15 uF [T491A156M006AT]
15 pF [C0603C150K5GACT U]	15 pF [C1206C150KGGAC TU]	15 uF [C1210C156K9PACT U]	15 uF [T491B156M004AT]
15 pF [C0805C150K1GACT U]	15 pF [C1210C150KBGAC TU]	15 uF [T409E156M004AH 4250]	15 uF [T491B156M006AT]
15 pF [C0805C150K2GACT U]	15 pF [C1812C150KBGAC TU]	15 uF [T409H156M025AH 4250]	15 uF [T491B156M010AT]
15 pF [C0805C150K3GACT U]	15 pF [C1825C150KBGAC TU]	15 uF [T419B156M004AH 4250]	15 uF [T491B156M025AT]
15 pF [C0805C150K4GACT U]	15 pF [C2220C150KBGAC TU]	15 uF [T419D156M010AH 4250]	15 uF [T491C156M006AT]
15 pF [C0805C150K5GACT U]	15 pF [C2225C150KBGAC TU]	15 uF [T429B156M004AH 4250]	15 uF [T491C156M010AT]
			15 uF [T491C156M016AT]

Multisim 14.0 Base Components

15 uF [T491C156M025AT]	15 uF [T494A156M004AT]	15 uF [T494D156M035AT]	15 uF [T495D156M020AT E275]
15 uF [T491D156M020AT]	15 uF [T494A156M006AT]	15 uF [T494S156M004AT]	15 uF [T495D156M025AT E100]
15 uF [T491D156M025AT]	15 uF [T494A156M010AT]	15 uF [T494S156M006AT]	15 uF [T495D156M025AT E275]
15 uF [T491D156M035AT]	15 uF [T494B156M004AT]	15 uF [T494T156M004AT]	15 uF [T495D156M035AT E225]
15 uF [T491S156M004AT]	15 uF [T494B156M010AT]	15 uF [T494T156M010AT]	15 uF [T495D156M035AT E300]
15 uF [T491S156M006AT]	15 uF [T494B156M016AT]	15 uF [T494U156M010AT]	15 uF [T495X156M025AT E200]
15 uF [T491T156M004AT]	15 uF [T494B156M025AT]	15 uF [T494U156M016AT]	15 uF [T495X156M035AT E200]
15 uF [T491T156M006AT]	15 uF [T494C156M006AT]	15 uF [T494X156M035AT]	15 uF [T495X156M050AT E200]
15 uF [T491T156M010AT]	15 uF [T494C156M010AT]	15 uF [T494X156M050AT]	15 uF [T495X156M050AT E300]
15 uF [T491U156M010AT]	15 uF [T494C156M016AT]	15 uF [T495B156M010AT E500]	15 uF [T497E156M010AT 6110]
15 uF [T491U156M016AT]	15 uF [T494C156M020AT]	15 uF [T495C156M010AT E375]	15 uF [T498B156M006AT E1K8]
15 uF [T491X156M035AT]	15 uF [T494D156M020AT]	15 uF [T495C156M010AT E400]	
15 uF [T491X156M050AT]	15 uF [T494D156M025AT]		

Multisim 14.0 Base Components

15 uF [T498B156M010AT E1K5]	15 uF [T520T156M006AT E100]	150 nF [C0603C154K5RACT U]	150 nF [C1206C154K2RACT U]
15 uF [T498C156M010AT E1K8]	15 uF [T520T156M12RAT E080]	150 nF [C0603C154K8RACT U]	150 nF [C1206C154K3RACT U]
15 uF [T498C156M016AT E1K1]	15 uF [T521B156M016AT E090]	150 nF [C0603C154M3VAC TU]	150 nF [C1206C154K4RACT U]
15 uF [T498D156M025AT E700]	15 uF [T521V156M025AT E090]	150 nF [C0603C154M4VAC TU]	150 nF [C1206C154K5RACT U]
15 uF [T499B156M006AT E3K5]	15 uF [T521V156M035AT E100]	150 nF [C0603C154M8VAC TU]	150 nF [C1206C154M5UAC TU]
15 uF [T499D156M020AT E1K0]	15 uF [T521V156M035AT E125]	150 nF [C0805C154K3RACT U]	150 nF [C1206F154K1RACT U]
15 uF [T513D156M035AH 6110]	15 uF [T521X156M063AT E035]	150 nF [C0805C154K4RACT U]	150 nF [C1206F154K3RACT U]
15 uF [T520A156M010AT E080]	15 uF [T521X156M063AT E150]	150 nF [C0805C154K5RACT U]	150 nF [C1206F154K4RACT U]
15 uF [T520D156M025AT E060]	15 uF [T541X156M063AH 6510]	150 nF [C0805C154K8RACT U]	150 nF [C1206F154K5RACT U]
15 uF [T520D156M025AT E080]	15 uF [T543T156M006AT E100]	150 nF [C0805C154M3VAC TU]	150 nF [C1210C154K1RACT U]
15 uF [T520T156M004AT E100]	15_AMP 150 nF [C0603C154K4RACT U]	150 nF [C1206C154K1RACT U]	150 nF [C1210C154K3HACT U]

Multisim 14.0 Base Components

150 nF [C1210C154K5HACT U]	150 nF [C1812C154K5HACT U]	150 nF [C2220C154K5GACT U]	150 pF [C0402C151K4RACT U]
150 nF [C1210C154K5RACT U]	150 nF [C1812C154K5RACT U]	150 nF [C2225C154K1RACT U]	150 pF [C0402C151K5GACT U]
150 nF [C1210F154K1RACT U]	150 nF [C1812C154M1UAC TU]	150 nF [C2225C154K2RACT U]	150 pF [C0402C151K5HACT U]
150 nF [C1210F154K3RACT U]	150 nF [C1812C154M5UAC TU]	150 nF [T429A154M050AH 4250]	150 pF [C0402C151K5RACT U]
150 nF [C1210F154K4RACT U]	150 nF [C1812F154K1RACT U]	150 nF [T491A154M035AT]	150 pF [C0402C151K8RACT U]
150 nF [C1210F154K5RACT U]	150 nF [C1812F154K2RACT U]	150 nF [T491A154M050AT]	150 pF [C0603C151K1GACT U]
150 nF [C1812C154K1GACT U]	150 nF [C1812F154K3RACT U]	150 nF [T491B154M050AT]	150 pF [C0603C151K3GACT U]
150 nF [C1812C154K1HACT U]	150 nF [C1812F154K5RACT U]	150 nF [T494A154M035AT]	150 pF [C0603C151K4GACT U]
150 nF [C1812C154K1RACT U]	150 nF [C1812F154K5RACT U]	150 nF [T494A154M050AT]	150 pF [C0603C151K4GACT U]
150 nF [C1812C154K2RACT U]	150 nF [C1812F154K5RACT U]	150 nF [T494B154M050AT]	150 pF [C0603C151K5GACT U]
150 nF [C1812C154K5GACT U]	150 nF [C1825C154K1RACT U]	150 pF [C0402C151K1HACT U]	150 pF [C0603C151K5GACT U]
	150 nF [C1825C154K5RACT U]	150 pF [C0402C151K3HACT U]	150 pF [C0805C151K1GACT U]
	150 nF [C2220C154K1GACT U]	150 pF [C0402C151K3RACT U]	150 pF [C0805C151K2GACT U]

Multisim 14.0 Base Components

150 pF [C0805C151K3GACT U]	150 pF [C2225C151KBGAC TU]	150 uF [A700X157M006AT E010]	150 uF [T491D157M010AT]
150 pF [C0805C151K4GACT U]	150 pF [CA064C151K4GAC TU]	150 uF [A700X157M006AT E015]	150 uF [T491D157M016AT]
150 pF [C0805C151K5GACT U]	150 pF [CA064C151K5GAC TU]	150 uF [A700X157M010AT E010]	150 uF [T491V157M004AT]
150 pF [C1206C151K1GACT U]	150 uF [A700D157M004AT E015]	150 uF [A700X157M010AT E015]	150 uF [T491V157M006AT]
150 pF [C1206C151K2GACT U]	150 uF [A700D157M004AT E018]	150 uF [T429G157M006AH 4250]	150 uF [T491X157M010AT]
150 pF [C1206C151K5GACT U]	150 uF [A700D157M2R5AT E015]	150 uF [T429X157M010AH 4250]	150 uF [T491X157M016AT]
150 pF [C1206C151KBGAC TU]	150 uF [A700D157M2R5AT E018]	150 uF [T491B157M004AT]	150 uF [T491X157M020AT]
150 pF [C1210C151KBGAC TU]	150 uF [A700V157M002AT E009]	150 uF [T491C157M004AT]	150 uF [T494B157M004AT]
150 pF [C1812C151KBGAC TU]	150 uF [A700V157M002AT E018]	150 uF [T491C157M010AT]	150 uF [T494C157M004AT]
150 pF [C1825C151KBGAC TU]	150 uF [A700V157M002AT E025]	150 uF [T491D157M004AT]	150 uF [T494C157M006AT]
150 pF [C2220C151KBGAC TU]	150 uF [A700V157M002AT E028]	150 uF [T491D157M006AT]	150 uF [T494D157M004AT]
			150 uF [T494D157M006AT]

Multisim 14.0 Base Components

150 uF [T494D157M010AT]	150 uF [T495D157M010AT E060]	150 uF [T495X157M016AT E100]	150 uF [T520B157M004AT E025]
150 uF [T494D157M016AT]	150 uF [T495D157M010AT E100]	150 uF [T510X157M016AT E030]	150 uF [T520B157M004AT E030]
150 uF [T494V157M004AT]	150 uF [T495D157M016AT E060]	150 uF [T510X157M016AT E040]	150 uF [T520B157M004AT E035]
150 uF [T494V157M006AT]	150 uF [T495D157M016AT E085]	150 uF [T513X157M016AH 6110]	150 uF [T520B157M004AT E040]
150 uF [T494V157M010AT]	150 uF [T495D157M016AT E100]	150 uF [T513X157M016AH 6120]	150 uF [T520B157M004AT E070]
150 uF [T494X157M010AT]	150 uF [T495D157M016AT E100]	150 uF [T513X157M016AH 6120]	150 uF [T520B157M004AT E070]
150 uF [T494X157M016AT]	150 uF [T495D157M016AT E125]	150 uF [T520B157M003AT E025]	150 uF [T520B157M006AT E035]
150 uF [T494X157M020AT]	150 uF [T495D157M016AT E150]	150 uF [T520B157M003AT E035]	150 uF [T520B157M006AT E045]
150 uF [T495B157M004AT E900]	150 uF [T495D157M016AT E150]	150 uF [T520B157M003AT E035]	150 uF [T520B157M006AT E045]
150 uF [T495C157M006AT E200]	150 uF [T495V157M010AT E150]	150 uF [T520B157M003AT E040]	150 uF [T520B157M006AT E070]
150 uF [T495D157M006AT E050]	150 uF [T495X157M010AT E085]	150 uF [T520B157M003AT E070]	150 uF [T520C157M004AT E015]
150 uF [T495D157M006AT E125]	150 uF [T495X157M010AT E100]	150 uF [T520B157M004AT E015]	150 uF [T520C157M004AT E025]
150 uF [T495D157M010AT E050]	150 uF [T495X157M016AT E075]	150 uF [T520B157M004AT E018]	150 uF [T520C157M004AT E045]

Multisim 14.0 Base Components

150 uF [T520C157M004AT E100]	150 uF [T520D157M006AT E055]	150 uF [T520U157M006AT E045]	150 uF [T520V157M006AT E012]
150 uF [T520C157M006AT E015]	150 uF [T520D157M008AT E025]	150 uF [T520U157M006AT E055]	150 uF [T520V157M006AT E015]
150 uF [T520C157M006AT E025]	150 uF [T520D157M008AT E040]	150 uF [T520U157M2R5AT E055]	150 uF [T520V157M006AT E018]
150 uF [T520C157M006AT E045]	150 uF [T520D157M008AT E055]	150 uF [T520V157M004AT E007]	150 uF [T520V157M006AT E025]
150 uF [T520C157M006AT E055]	150 uF [T520D157M010AT E025]	150 uF [T520V157M004AT E009]	150 uF [T520V157M006AT E040]
150 uF [T520C157M010AT E055]	150 uF [T520D157M010AT E040]	150 uF [T520V157M004AT E012]	150 uF [T520V157M006AT E045]
150 uF [T520D157M004AT E007]	150 uF [T520D157M010AT E055]	150 uF [T520V157M004AT E015]	150 uF [T520V157M010AT E018]
150 uF [T520D157M006AT E006]	150 uF [T520L157M006AT E012]	150 uF [T520V157M004AT E025]	150 uF [T520V157M010AT E040]
150 uF [T520D157M006AT E007]	150 uF [T520L157M006AT E025]	150 uF [T520V157M006AT E006]	150 uF [T520W157M006AT E025]
150 uF [T520D157M006AT E015]	150 uF [T520M157M006AT E070]	150 uF [T520V157M006AT E007]	150 uF [T520W157M006AT E040]
150 uF [T520D157M006AT E025]	150 uF [T520U157M004AT E055]	150 uF [T520V157M006AT E009]	150 uF [T520X157M016AT E040]

Multisim 14.0 Base Components

150 uF [T522V157M006AT E040]	150 uF [T530X157M016AT E025]	16 pF [C2220C160KBGAC TU]	160 pF [C2220C161KBGAC TU]
150 uF [T525B157M003AT E080]	150 uF [T530X157M016AT E040]	16 pF [C2225C160KBGAC TU]	160 pF [C2225C161KBGAC TU]
150 uF [T525D157M006AT E025]	1-534206-0 1-534206-3	160 pF [C0402C161K1HACT U]	1-640455-0 171-009-113R001
150 uF [T525D157M010AT E025]	1-534206-7 15C02MH-TL-E	160 pF [C0402C161K3HACT U]	171-009-213R001 171-015-113R001
150 uF [T528Z157M006AT E007]	16 pF [C0603C160K2GACT U]	160 pF [C0402C161K5HACT U]	171-015-213R001 171-025-113R001
150 uF [T528Z157M006AT E008]	16 pF [C0603C160K5GACT U]	160 pF [C0805C161K3GACT U]	171-025-213R001 171-037-113R001
150 uF [T528Z157M006AT E009]	16 pF [C0805C160KBGAC TU]	160 pF [C0805C161K5GACT U]	171-037-213R001 171-050-113R001
150 uF [T528Z157M006AT E012]	16 pF [C1206C160KBGAC TU]	160 pF [C1206C161KBGAC TU]	171-050-213R001 1734035-1
150 uF [T530D157M010AT E006]	16 pF [C1210C160KBGAC TU]	160 pF [C1210C161KBGAC TU]	173-E09-113R001 173-E09-213R001
150 uF [T530D157M010AT E010]	16 pF [C1812C160KBGAC TU]	160 pF [C1812C161KBGAC TU]	173-E15-113R001 173-E15-213R001
150 uF [T530X157M016AT E015]	16 pF [C1825C160KBGAC TU]	160 pF [C1825C161KBGAC TU]	173-E25-113R001 173-E25-213R001
			173-E37-113R001 173-E37-213R001

Multisim 14.0 Base Components

173-E50-113R001	18 nF [C0603C183K3RACT U]	18 nF [C0805C183KARACT U]	18 nF [C1206C183K5RACT U]
173-E50-213R001			
174-E09-113R001	18 nF [C0603C183K4RACT U]	18 nF [C0805F183K1RACT U]	18 nF [C1210C183K1GACT U]
174-E09-213R001			
174-E15-113R001	18 nF [C0603C183K5RACT U]	18 nF [C0805F183K3RACT U]	18 nF [C1210C183K1HACT U]
174-E15-213R001			
174-E25-113R001	18 nF [C0603C183K8RACT U]	18 nF [C0805F183K4RACT U]	18 nF [C1210C183K3HACT U]
174-E25-213R001			
174-E37-113R001	18 nF [C0805C183K1RACT U]	18 nF [C0805F183K5RACT U]	18 nF [C1210C183K5GACT U]
174-E37-213R001			
174-E50-113R001	18 nF [C0805C183K3GACT U]	18 nF [C1206C183K1HACT U]	18 nF [C1210C183K5HACT U]
174-E50-213R001			
18 nF [C0402C183K4RACT U]	18 nF [C0805C183K3HACT U]	18 nF [C1206C183K1RACT U]	18 nF [C1210C183K5RACT U]
18 nF [C0402C183K8PACT U]	18 nF [C0805C183K4RACT U]	18 nF [C1206C183K2RACT U]	18 nF [C1210C183KARACT U]
18 nF [C0402C183K8RACT U]	18 nF [C0805C183K5HACT U]	18 nF [C1206C183K3GACT U]	18 nF [C1812C183K1GACT U]
18 nF [C0402C183K9PACT U]	18 nF [C0805C183K5RACT U]	18 nF [C1206C183K3HACT U]	18 nF [C1812C183K1HACT U]
18 nF [C0402C183K9RACT U]	18 nF [C0805C183K8RACT U]	18 nF [C1206C183K5HACT U]	18 nF [C1812C183K5GACT U]
18 nF [C0603C183K1RACT U]			

Multisim 14.0 Base Components

18 nF [C1812C183K5HACT U]	18 pF [C0603C180K8GACT U]	18 pF [C1825C180KBGAC TU]	180 nF [C0805C184K5RACT U]
18 nF [C2220C183K2GACT U]	18 pF [C0805C180K1GACT U]	18 pF [C2220C180KBGAC TU]	180 nF [C0805C184K8RACT U]
18 nF [CA064C183K3RAC]	18 pF [C0805C180K2GACT U]	18 pF [C2225C180KBGAC TU]	180 nF [C1206C184K1RACT U]
18 nF [CDR03BX183BKSM]	18 pF [C0805C180K3GACT U]	18 uF [C1210C186K4PACT U]	180 nF [C1206C184K5RACT U]
18 pF [C0201C180K3GACT U]	18 pF [C0805C180K5GACT U]	18 uF [C1210C186K8PACT U]	180 nF [C1206C184M5UAC TU]
18 pF [C0402C180K3GACT U]	18 pF [C0805C180KBGAC TU]	18 uF [C1210C186K9PACT U]	180 nF [C1206F184K1RACT U]
18 pF [C0402C180K5GACT U]	18 pF [C1206C180K1GACT U]	18 uF [T521X186M050AT E070]	180 nF [C1206F184K3RACT U]
18 pF [C0402C180K8GACT U]	18 pF [C1206C180K5GACT U]	180 nF [C0603C184K4RACT U]	180 nF [C1206F184K4RACT U]
18 pF [C0603C180K2GACT U]	18 pF [C1206C180KBGAC TU]	180 nF [C0603C184K8RACT U]	180 nF [C1206F184K5RACT U]
18 pF [C0603C180K3GACT U]	18 pF [C1210C180KBGAC TU]	180 nF [C0805C184K3RACT U]	180 nF [C1210C184K1RACT U]
18 pF [C0603C180K5GACT U]	18 pF [C1812C180KBGAC TU]	180 nF [C0805C184K4RACT U]	180 nF [C1210C184K3HACT U]

Multisim 14.0 Base Components

180 nF [C1210C184K5RACT U]	180 nF [C1812F184K5RACT U]	180 pF [C0603C181K2RACT U]	180 pF [C1206C181K5GACT U]
180 nF [C1210F184K1RACT U]	180 nF [C1825C184K5RACT U]	180 pF [C0603C181K3RACT U]	180 pF [C1206C181KBGAC TU]
180 nF [C1210F184K3RACT U]	180 nF [C2225C184K1RACT U]	180 pF [C0603C181K4RACT U]	180 pF [C1210C181KBGAC TU]
180 nF [C1210F184K4RACT U]	180 pF [C0402C181K1HACT U]	180 pF [C0603C181K5GACT U]	180 pF [C1812C181KBGAC TU]
180 nF [C1210F184K5RACT U]	180 pF [C0402C181K3HACT U]	180 pF [C0603C181K5RACT U]	180 pF [C1825C181KBGAC TU]
180 nF [C1812C184K1RACT U]	180 pF [C0402C181K3RACT U]	180 pF [C0603C181K8RACT U]	180 pF [C2220C181KBGAC TU]
180 nF [C1812C184K5HACT U]	180 pF [C0402C181K4RACT U]	180 pF [C0805C181K1GACT U]	180 pF [C2225C181KBGAC TU]
180 nF [C1812C184K5RACT U]	180 pF [C0402C181K5HACT U]	180 pF [C0805C181K2GACT U]	180 pF [CA064C181K4GAC TU]
180 nF [C1812F184K1RACT U]	180 pF [C0402C181K5RACT U]	180 pF [C0805C181K5GACT U]	180 pF [CA064C181K5GAC TU]
180 nF [C1812F184K2RACT U]	180 pF [C0402C181K8RACT U]	180 pF [C1206C181K1GACT U]	180 uF [A700D187M002AT E015]
180 nF [C1812F184K3RACT U]	180 pF [C0603C181K1RACT U]	180 pF [C1206C181K2GACT U]	180 uF [A700D187M002AT E018]

Multisim 14.0 Base Components

180 uF [A700D187M004AT E015]	181-078-213R431	1JH62	1N3880
	182-009-113R431	1LH62	1N3880A
180 uF [A700D187M004AT E018]	182-009-213R431	1N1199C	1N3881
	182-015-113R431	1N1200C	1N3881A
180 uF [A700D187M2R5AT E015]	182-015-213R431	1N1202C	1N3882
	182-025-113R431	1N1204C	1N3882A
	182-025-213R431	1N1206C	1N3883
180 uF [A700D187M2R5AT E018]	182-037-113R431	1N3064	1N3883A
	182-037-213R431	1N3208	1N3889
180 uF [A700X187M004AT E010]	183-009-113R161	1N3491	1N3889A
	183-009-213R161	1N3492	1N3890
180 uF [A700X187M006AT E010]	183-015-113R161	1N3493	1N3890A
	183-015-213R161	1N3494	1N3891
180 uF [A700X187M006AT E015]	183-025-113R161	1N3495	1N3891A
	183-025-213R161	1N3611GP	1N3892
	183-037-113R161	1N3612GP	1N3892A
181-015-113R431	183-037-213R161	1N3613GP	1N3893
181-015-213R431	1932258-1	1N3614GP	1N3893A
181-026-113R431	1981584-1	1N3659	1N3899
181-026-213R431	1B4B42	1N3660	1N3900
181-044-113R431	1BH62	1N3661	1N3901
181-044-213R431	1DH62	1N3662	1N3902
181-062-113R431	1G4B42	1N3663	1N3903
181-062-213R431	1GH62	1N3879	1N3909
181-078-113R431	1J4B42	1N3879A	1N3910

Multisim 14.0 Base Components

1N3911	1N4007G	1N4448	1N4746A
1N3912	1N4007GP	1N4449	1N4747A
1N3913	1N4007RLG	1N4454	1N4748A
1N3957GP	1N4009	1N4585GP	1N4749A
1N4001G	1N4148	1N4586GP	1N4750A
1N4001GP	1N4149	1N4678	1N4751A
1N4001RLG	1N4150	1N4681	1N4752A
1N4002G	1N4151	1N4728A	1N4753A
1N4002GP	1N4152	1N4729A	1N4754A
1N4002RLG	1N4153	1N4730A	1N4755A
1N4003G	1N4154	1N4731A	1N4756A
1N4003GP	1N4245GP	1N4732A	1N4757A
1N4003RLG	1N4246GP	1N4733A	1N4758A
1N4004G	1N4247GP	1N4734A	1N4759A
1N4004GP	1N4248GP	1N4735A	1N4760A
1N4004RLG	1N4249GP	1N4736A	1N4761A
1N4005G	1N4305	1N4737A	1N4762A
1N4005GP	1N4370A	1N4738A	1N4763A
1N4005RLG	1N4371A	1N4739A	1N4764A
1N4006FFG	1N4372A	1N4740A	1N4933
1N4006G	1N4383GP	1N4741A	1N4933G
1N4006GP	1N4384GP	1N4742A	1N4933RLG
1N4006RLG	1N4385GP	1N4743A	1N4934
1N4007-E3/54	1N4446	1N4744A	1N4934G
1N4007FFG	1N4447	1N4745A	1N4934RLG

Multisim 14.0 Base Components

1N4935	1N5227B	1N5252B	1N5277B
1N4935G	1N5228B	1N5253B	1N5278B
1N4935RLG	1N5229B	1N5254B	1N5279B
1N4936	1N5230B	1N5255B	1N5280B
1N4936G	1N5231B	1N5256B	1N5281B
1N4936RLG	1N5232B	1N5257B	1N5333BRLG
1N4937	1N5233B	1N5258B	1N5334BRLG
1N4937G	1N5234B	1N5259B	1N5335BG
1N4937RLG	1N5235B	1N5260B	1N5335BRLG
1N4938	1N5236B	1N5261B	1N5336BG
1N4942GP	1N5237B	1N5262B	1N5336BRLG
1N4944GP	1N5238B	1N5263B	1N5337BG
1N4946GP	1N5239B	1N5264B	1N5337BRLG
1N4947GP	1N5240B	1N5265B	1N5338BG
1N4948GP	1N5241B	1N5266B	1N5338BRLG
1N5059GP	1N5242B	1N5267B	1N5339BG
1N5060GP	1N5243B	1N5268B	1N5339BRLG
1N5061GP	1N5244B	1N5269B	1N5340BG
1N5062GP	1N5245B	1N5270B	1N5340BRLG
1N5221B	1N5246B	1N5271B	1N5341BG
1N5222B	1N5247B	1N5272B	1N5341BRLG
1N5223B	1N5248B	1N5273B	1N5342BG
1N5224B	1N5249B	1N5274B	1N5342BRLG
1N5225B	1N5250B	1N5275B	1N5343BG
1N5226B	1N5251B	1N5276B	1N5343BRLG

Multisim 14.0 Base Components

1N5344BG	1N5358BRLG	1N5373BRLG	1N5399GP
1N5344BRLG	1N5359BG	1N5374BG	1N5400
1N5345BRLG	1N5359BRLG	1N5374BRLG	1N5400G
1N5346BG	1N5361BG	1N5375BG	1N5400RLG
1N5346BRLG	1N5361BRLG	1N5375BRLG	1N5401
1N5347BG	1N5362BG	1N5378BG	1N5401G
1N5347BRLG	1N5362BRLG	1N5378BRLG	1N5401RLG
1N5348BG	1N5363BG	1N5381BRLG	1N5402
1N5348BRLG	1N5363BRLG	1N5383BG	1N5402G
1N5349BG	1N5364BG	1N5383BRLG	1N5402RLG
1N5349BRLG	1N5364BRLG	1N5384BG	1N5404
1N5350BG	1N5365BG	1N5384BRLG	1N5404G
1N5350BRLG	1N5365BRLG	1N5386BG	1N5404RLG
1N5351BG	1N5366BG	1N5386BRLG	1N5406
1N5351BRLG	1N5366BRLG	1N5388BG	1N5406G
1N5352BG	1N5367BG	1N5388BRLG	1N5406RLG
1N5352BRLG	1N5367BRLG	1N5391	1N5407G
1N5353BG	1N5368BG	1N5391GP	1N5407RLG
1N5353BRLG	1N5368BRLG	1N5392GP	1N5408-E3/54
1N5355BG	1N5369BG	1N5393GP	1N5408G
1N5355BRLG	1N5369BRLG	1N5394GP	1N5408RLG
1N5356BRLG	1N5371BRLG	1N5395GP	1N5615GP
1N5357BG	1N5372BG	1N5396GP	1N5617GP
1N5357BRLG	1N5372BRLG	1N5397GP	1N5619GP
1N5358BG	1N5373BG	1N5398GP	1N5621GP

Multisim 14.0 Base Components

1N5623GP	1N5823	1N5921BG	1N5934BRLG
1N5758	1N5824	1N5921BRLG	1N5935B
1N5758A	1N5825	1N5922B	1N5935BRLG
1N5759	1N5826	1N5923B	1N5936B
1N5759A	1N5827	1N5923BRLG	1N5937B
1N5760	1N5828	1N5924B	1N5937BRLG
1N5761	1N5829	1N5924BRLG	1N5938B
1N5761A	1N5830	1N5925B	1N5938BRLG
1N5817-E3/54	1N5831	1N5925BRLG	1N5939B
1N5817G	1N5832	1N5926B	1N5940B
1N5817RLG	1N5833	1N5927B	1N5940BRLG
1N5818G	1N5834	1N5927BG	1N5941B
1N5818RLG	1N5913B	1N5927BRLG	1N5941BRLG
1N5819G	1N5913BRLG	1N5928B	1N5942B
1N5819RLG	1N5914B	1N5929B	1N5942BRLG
1N5820	1N5915B	1N5929BG	1N5943B
1N5820G	1N5916B	1N5929BRLG	1N5944B
1N5820RLG	1N5917B	1N5930B	1N5945B
1N5821	1N5918B	1N5931B	1N5946B
1N5821G	1N5919B	1N5931BRLG	1N5946BRLG
1N5821RLG	1N5919BG	1N5932B	1N5947B
1N5822	1N5919BRLG	1N5932BRLG	1N5948BRLG
1N5822-E3/54	1N5920B	1N5933B	1N5953BG
1N5822G	1N5920BG	1N5934B	1N5953BRLG
1N5822RLG	1N5921B	1N5934BG	1N5955BRLG

Multisim 14.0 Base Components

1N5956BG	1N6008B	1N6292ARL4G	1N914B
1N5956BRLG	1N6009B	1N6294ARL4G	1N916
1N5985B	1N6010B	1N6373-E3/51	1N916A
1N5986B	1N6011B	1N6478	1N916B
1N5987B	1N6012B	1N6479	1N957B
1N5988B	1N6013B	1N6480	1N958B
1N5989B	1N6014B	1N6481	1N959B
1N5990B	1N6015B	1N6482	1N960B
1N5991B	1N6016B	1N6483	1N961B
1N5992B	1N6017B	1N6484	1N962B
1N5993B	1N6018B	1N747A	1N963B
1N5994B	1N6019B	1N748A	1N964B
1N5995B	1N6020B	1N749A	1N965B
1N5996B	1N6021B	1N750A	1N966B
1N5997B	1N6022B	1N751A	1N967B
1N5998B	1N6023B	1N752A	1N968B
1N5999B	1N6024B	1N753A	1N969B
1N6000B	1N6025B	1N754A	1N970B
1N6001B	1N6096	1N755A	1N971B
1N6002B	1N6098	1N756A	1N972B
1N6003B	1N6285AG	1N757A	1N973B
1N6004B	1N6285ARL4G	1N758A	1N974B
1N6005B	1N6287AG	1N759A	1N975B
1N6006B	1N6287ARL4G	1N914	1N976B
1N6007B	1N6292AG	1N914A	1N977B

Multisim 14.0 Base Components

1N978B	1PS301	1PS79SB30	1SMA5921BT3G
1N979B	1PS302	1PS79SB31	1SMA5922BT3G
1N980B	1PS66SB17	1PS79SB40	1SMA5927BT3G
1N981B	1PS66SB82	1PS79SB70	1SMA5931BT3G
1N982B	1PS70SB10	1PS88SB48	1SMA5932BT3G
1N983B	1PS70SB14	1PS88SB82	1SMA5936BT3G
1N984B	1PS70SB15	1S1553	1SMA5940BT3G
1N985B	1PS70SB16	1S1554	1SMB12AT3G
1N986B	1PS70SB20	1S1555	1SMB14AT3G
1N987B	1PS70SB40	1S1830	1SMB170AT3G
1N988B	1PS70SB44	1S1834	1SMB18CAT3G
1N989B	1PS70SB45	1S1835	1SMB20CAT3G
1N990B	1PS70SB46	1S1885	1SMB22CAT3G
1N991B	1PS70SB82	1S1887	1SMB24AT3G
1N992B	1PS70SB84	1S1888	1SMB24CAT3G
1P1S	1PS70SB85	1S953	1SMB26CAT3G
1P2S	1PS70SB86	1S954	1SMB28AT3G
1P3S	1PS74SB23	1S955	1SMB28CAT3G
1PMT12AT1G	1PS75SB45	1SMA12CAT3G	1SMB30AT3G
1PMT16AT3G	1PS76SB10	1SMA26AT3G	1SMB30CAT3G
1PMT33AT3G	1PS76SB17	1SMA30AT3G	1SMB33CAT3G
1PMT5.0AT1G	1PS76SB40	1SMA40CAT3G	1SMB36CAT3G
1PMT5927BT1G	1PS76SB70	1SMA5.0AT3G	1SMB5.0AT3G
1PS10SB82	1PS79SB10	1SMA5913BT3G	1SMB54CAT3G
1PS300	1PS79SB17	1SMA5918BT3G	1SMB58CAT3G

Multisim 14.0 Base Components

1SMB5914BT3G	1Z12	2 nF [C0603C202K3HACT U]	2.2 nF [C0603C222K1HACT U]
1SMB5918BT3G	1Z13		
1SMB5919BT3G	1Z14	2 nF [C0603C202K5HACT U]	2.2 nF [C0603C222K1RACT U]
1SMB5920BT3G	1Z15		
1SMB5921BT3G	1Z30	2 nF	2.2 nF
1SMB5922BT3G	1Z6.2	[C1210C202KCGAC TU]	[C0603C222K2RACT U]
1SMB5924BT3G	1Z6.8		
1SMB5925BT3G	1Z7.5	2 nF [C1812C202KBGAC TU]	2.2 nF [C0603C222K3GACT U]
1SMB5927BT3G	1Z8.2		
1SMB5930BT3G	1Z9.1	2 nF [C1825C202KBGAC TU]	2.2 nF [C0603C222K3HACT U]
1SMB5931BT3G	1ZB10		
1SMB5933BT3G	1ZB11	2 nF [C2220C202KBGAC TU]	2.2 nF [C0603C222K3RACT U]
1SMB5934BT3G	1ZB12		
1SMB5935BT3G	1ZB13	2 nF	2.2 nF
1SMB5936BT3G	1ZB14	[C2225C202KBGAC TU]	[C0603C222K4RACT U]
1SMB5937BT3G	1ZB15		
1SMB5939BT3G	1ZB30	2.2 nF [C0402C222K3RACT U]	2.2 nF [C0603C222K5HACT U]
1SMB5940BT3G	1ZB6.8		
1SMB70AT3G	1ZB7.5	2.2 nF [C0402C222K4RACT U]	2.2 nF [C0603C222K5RACT U]
1SMB85AT3G	1ZB8.2		
1SMC28AT3G	1ZB9.1	2.2 nF [C0402C222K5RACT U]	2.2 nF [C0603C222K8RACT U]
1SMC36AT3G	2 nF [C0603C202K1HACT U]		
1SMC6.0AT3G		2.2 nF [C0402C222K8RACT U]	2.2 nF [C0603C222K9RACT U]
1Z10			
1Z11			

Multisim 14.0 Base Components

2.2 nF [C0805C222K1GACT U]	2.2 nF [C1206C222K1RACT U]	2.2 nF [C1812C222KBGAC TU]	2.2 uF [C0603C225K9PACT U]
2.2 nF [C0805C222K1HACT U]	2.2 nF [C1206C222K2RACT U]	2.2 nF [C1812C222KDGAC TU]	2.2 uF [C0805C225K4PACT U]
2.2 nF [C0805C222K1RACT U]	2.2 nF [C1206C222K4RACT U]	2.2 nF [C1825C222KBGAC TU]	2.2 uF [C0805C225K4RACT U]
2.2 nF [C0805C222K2RACT U]	2.2 nF [C1206C222K5GACT U]	2.2 nF [C2220C222KBGAC TU]	2.2 uF [C0805C225K8PACT U]
2.2 nF [C0805C222K3GACT U]	2.2 nF [C1206C222K5RACT U]	2.2 nF [C2225C222KBGAC TU]	2.2 uF [C0805C225K8RACT U]
2.2 nF [C0805C222K3HACT U]	2.2 nF [C1210C222K1GACT U]	2.2 nF [CA064C222K1RACT U]	2.2 uF [C0805C225K9PACT U]
2.2 nF [C0805C222K3RACT U]	2.2 nF [C1210C222K1RACT U]	2.2 nF [CA064C222K4RACT U]	2.2 uF [C0805C225K9RACT U]
2.2 nF [C0805C222K5HACT U]	2.2 nF [C1210C222K2GACT U]	2.2 nF [CA064C222K5RACT U]	2.2 uF [C0805C225M4VAC TU]
2.2 nF [C0805C222K5RACT U]	2.2 nF [C1210C222K5GACT U]	2.2 uF [C0402C225K9PACT U]	2.2 uF [C0805C225M8VAC TU]
2.2 nF [C0805C222KARACT U]	2.2 nF [C1210C222KCGAC TU]	2.2 uF [C0603C225K4PACT U]	2.2 uF [C1206C225K3NAC TU]
2.2 nF [C1206C222K1GACT U]	2.2 nF [C1812C222K2GACT U]	2.2 uF [C0603C225K8PACT U]	2.2 uF [C1206C225K3PACT U]

Multisim 14.0 Base Components

2.2 uF [C1206C225K4PACT U]	2.2 uF [C1210C225K5RACT U]	2.2 uF [T429A225M010AH 4250]	2.2 uF [T491D225M050AT]
2.2 uF [C1206C225K4RACT U]	2.2 uF [C1210C225K8RACT U]	2.2 uF [T429C225M015AH 4250]	2.2 uF [T491S225M016AT]
2.2 uF [C1206C225K8PACT U]	2.2 uF [C1210C225K9PACT U]	2.2 uF [T491A225M006AT]	2.2 uF [T494A225M006AT]
2.2 uF [C1206C225K8RACT U]	2.2 uF [C1210C225K9RACT U]	2.2 uF [T491A225M010AT]	2.2 uF [T494A225M010AT]
2.2 uF [C1206C225K9PACT U]	2.2 uF [C1210C225M8VAC TU]	2.2 uF [T491A225M016AT]	2.2 uF [T494A225M016AT]
2.2 uF [C1206C225K9RACT U]	2.2 uF [C1812C225K1RACT U]	2.2 uF [T491A225M020AT]	2.2 uF [T494A225M020AT]
2.2 uF [C1206C225K9RACT U]	2.2 uF [C1812C225K1RACT U]	2.2 uF [T491A225M025AT]	2.2 uF [T494B225M020AT]
2.2 uF [C1206C225M4VAC TU]	2.2 uF [C1825C225K5RACT U]	2.2 uF [T491B225M010AT]	2.2 uF [T494B225M025AT]
2.2 uF [C1210C225K1RACT U]	2.2 uF [C2220C225K5RACT U]	2.2 uF [T491B225M020AT]	2.2 uF [T494B225M035AT]
2.2 uF [C1210C225K3PACT U]	2.2 uF [C2225C225K5RACT U]	2.2 uF [T491B225M025AT]	2.2 uF [T494C225M025AT]
2.2 uF [C1210C225K3PACT U]	2.2 uF [C2225C225K5RACT U]	2.2 uF [T491B225M035AT]	2.2 uF [T494C225M035AT]
2.2 uF [C1210C225K3RACT U]	2.2 uF [C2225C225M5UAC TU]	2.2 uF [T491C225M025AT]	2.2 uF [T494C225M050AT]
2.2 uF [C1210C225K4RACT U]	2.2 uF [T409C225M015AH 4250]	2.2 uF [T491C225M035AT]	2.2 uF [T494D225M050AT]
		2.2 uF [T491C225M050AT]	2.2 uF [T494S225M016AT]

Multisim 14.0 Base Components

2.2 uF [T498A225M010AT E4K6]	2.4 nF [C2225C242KBGAC TU]	2.7 nF [C0603C272K5RACT U]	2.7 nF [C0805C272K5HACT U]
2.2 uF [T498B225M025AT E3K0]	2.7 nF [C0402C272K3RACT U]	2.7 nF [C0603C272K8RACT U]	2.7 nF [C0805C272K5RACT U]
2.4 nF [C0603C242K1HACT U]	2.7 nF [C0402C272K4RACT U]	2.7 nF [C0805C272K1GACT U]	2.7 nF [C0805C272KARACT U]
2.4 nF [C0603C242K3HACT U]	2.7 nF [C0402C272K5RACT U]	2.7 nF [C0805C272K1HACT U]	2.7 nF [C1206C272K1GACT U]
2.4 nF [C0603C242K5HACT U]	2.7 nF [C0603C272K1HACT U]	2.7 nF [C0805C272K1RACT U]	2.7 nF [C1206C272K1RACT U]
2.4 nF [C0805C242K1GACT U]	2.7 nF [C0603C272K1RACT U]	2.7 nF [C0805C272K2RACT U]	2.7 nF [C1206C272K2RACT U]
2.4 nF [C0805C242K1HACT U]	2.7 nF [C0603C272K3GACT U]	2.7 nF [C0805C272K3GACT U]	2.7 nF [C1206C272K5GACT U]
2.4 nF [C0805C242K3HACT U]	2.7 nF [C0603C272K3HACT U]	2.7 nF [C0805C272K3HACT U]	2.7 nF [C1206C272K5RACT U]
2.4 nF [C0805C242K5HACT U]	2.7 nF [C0603C272K3RACT U]	2.7 nF [C0805C272K3RACT U]	2.7 nF [C1210C272K2GACT U]
2.4 nF [C1825C242KBGAC TU]	2.7 nF [C0603C272K4RACT U]	2.7 nF [C0805C272K4GACT U]	2.7 nF [C1210C272K5GACT U]
2.4 nF [C2220C242KBGAC TU]	2.7 nF [C0603C272K5HACT U]	2.7 nF [C0805C272K4RACT U]	2.7 nF [C1210C272KCGAC TU]

Multisim 14.0 Base Components

2.7 nF [C1812C272K1GACT U]	2.7 uF [C1206C275K9RACT U]	20 pF [C1206C200K5GACT U]	200 pF [C0603C201K5GACT U]
2.7 nF [C1812C272K5GACT U]	2_AMP 20 pF [C0402C200K5GACT U]	20 pF [C1206C200KBGAC TU]	200 pF [C0805C201K2GACT U]
2.7 nF [C1825C272KBGAC TU]	20 pF [C0402C200K8GACT U]	20 pF [C1206C200KCGAC TU]	200 pF [C0805C201K5GACT U]
2.7 nF [C2220C272KBGAC TU]	20 pF [C0603C200K2GACT U]	20 pF [C1210C200KBGAC TU]	200 pF [C1206C201K5GACT U]
2.7 nF [C2225C272KBGAC TU]	20 pF [C0603C200K4GACT U]	20 pF [C1812C200KBGAC TU]	200 pF [C1206C201KBGAC TU]
2.7 uF [C0805C275K8PACT U]	20 pF [C0603C200K5GACT U]	20 pF [C1825C200KBGAC TU]	200 pF [C1210C201KBGAC TU]
2.7 uF [C1206C275K3PACT U]	20 pF [C0805C200K1GACT U]	20 pF [C2220C200KBGAC TU]	200 pF [C1812C201KBGAC TU]
2.7 uF [C1206C275K4PACT U]	20 pF [C0805C200K2GACT U]	20 pF [C2225C200KBGAC TU]	200 pF [C2220C201KBGAC TU]
2.7 uF [C1206C275K4RACT U]	20 pF [C0805C200K5GACT U]	20_AMP 200 pF [C0402C201K1HACT U]	200 pF [C2225C201KBGAC TU]
2.7 uF [C1206C275K8RACT U]	20 pF [C0805C200KBGAC TU]	200 pF [C0402C201K3HACT U]	2013655-1
2.7 uF [C1206C275K9PACT U]	20 pF [C1206C200K1GACT U]	200 pF [C0402C201K5HACT U]	22 nF [C0402C223K3RACT U]
			22 nF [C0402C223K4RACT U]

Multisim 14.0 Base Components

22 nF [C0402C223K5RACT U]	22 nF [C0603C223M8VAC TU]	22 nF [C0805C223M5UAC TU]	22 nF [C1206C223K4RACT U]
22 nF [C0402C223K8PACT U]	22 nF [C0805C223K1RACT U]	22 nF [C0805F223K1RACT U]	22 nF [C1206C223K5HACT U]
22 nF [C0402C223K8RACT U]	22 nF [C0805C223K2RACT U]	22 nF [C0805F223K3RACT U]	22 nF [C1206C223K5RACT U]
22 nF [C0402C223K9PACT U]	22 nF [C0805C223K3GACT U]	22 nF [C0805F223K4RACT U]	22 nF [C1206C223M5UAC TU]
22 nF [C0402C223K9RACT U]	22 nF [C0805C223K3HACT U]	22 nF [C0805F223K5RACT U]	22 nF [C1206F223K2RACT U]
22 nF [C0603C223K1RACT U]	22 nF [C0805C223K3RACT U]	22 nF [C1206C223K1HACT U]	22 nF [C1210C223K1GACT U]
22 nF [C0603C223K3RACT U]	22 nF [C0805C223K4RACT U]	22 nF [C1206C223K1RACT U]	22 nF [C1210C223K1HACT U]
22 nF [C0603C223K4RACT U]	22 nF [C0805C223K5HACT U]	22 nF [C1206C223K2RACT U]	22 nF [C1210C223K1RACT U]
22 nF [C0603C223K5RACT U]	22 nF [C0805C223K5RACT U]	22 nF [C1206C223K3GACT U]	22 nF [C1210C223K2RACT U]
22 nF [C0603C223K8RACT U]	22 nF [C0805C223K8RACT U]	22 nF [C1206C223K3HACT U]	22 nF [C1210C223K3GACT U]
22 nF [C0603C223M3VAC TU]	22 nF [C0805C223KARACT U]	22 nF [C1206C223K3RACT U]	22 nF [C1210C223K3HACT U]

Multisim 14.0 Base Components

22 nF [C1210C223K5GACT U]	22 nF [C1825C223K1GACT U]	22 pF [C0402C220K8GACT U]	22 pF [C0805C220KCGAC TU]
22 nF [C1210C223K5HACT U]	22 nF [C1825C223K5GACT U]	22 pF [C0603C220K1GACT U]	22 pF [C0805C220KDGAC TU]
22 nF [C1210C223K5RACT U]	22 nF [C1825C223K5RACT U]	22 pF [C0603C220K2GACT U]	22 pF [C1206C220K1GACT U]
22 nF [C1210C223KARACT U]	22 nF [C2220C223K1GACT U]	22 pF [C0603C220K3GACT U]	22 pF [C1206C220K2GACT U]
22 nF [C1812C223K1GACT U]	22 nF [C2220C223K2GACT U]	22 pF [C0603C220K4GACT U]	22 pF [C1206C220K5GACT U]
22 nF [C1812C223K1HACT U]	22 nF [C2225C223K1GACT U]	22 pF [C0603C220K5GACT U]	22 pF [C1206C220KBGAC TU]
22 nF [C1812C223K1RACT U]	22 nF [C2225C223K5GACT U]	22 pF [C0805C220K1GACT U]	22 pF [C1206C220KCGAC TU]
22 nF [C1812C223K2RACT U]	22 pF [C0201C220K3GACT U]	22 pF [C0805C220K2GACT U]	22 pF [C1206C220KDGAC TU]
22 nF [C1812C223K5GACT U]	22 pF [C0402C220K3GACT U]	22 pF [C0805C220K3GACT U]	22 pF [C1210C220K2GACT U]
22 nF [C1812C223K5HACT U]	22 pF [C0402C220K4GACT U]	22 pF [C0805C220K5GACT U]	22 pF [C1210C220K5GACT U]
22 nF [C1812C223K5RACT U]	22 pF [C0402C220K5GACT U]	22 pF [C0805C220KBGAC TU]	22 pF [C1210C220KBGAC TU]

Multisim 14.0 Base Components

22 pF [C1812C220KBGAC TU]	22 uF [A700V226M006AT E045]	22 uF [C1210C226K9PACT U]	22 uF [T491C226M004AT]
22 pF [C1825C220KBGAC TU]	22 uF [A700V226M008AT E028]	22 uF [C1210C226K9RACT U]	22 uF [T491C226M006AT]
22 pF [C2220C220KBGAC TU]	22 uF [A700V226M008AT E045]	22 uF [C1210C226M8VAC TU]	22 uF [T491C226M010AT]
22 pF [C2225C220KBGAC TU]	22 uF [A700V226M010AT E028]	22 uF [T419G226M020AH 4250]	22 uF [T491C226M020AT]
22 pF [CA064C220K2GAC TU]	22 uF [A700V226M12RAT E030]	22 uF [T429D226M006AH 4250]	22 uF [T491C226M025AT]
22 pF [CA064C220K3GAC TU]	22 uF [C0805C226K9PACT U]	22 uF [T491A226M004AT]	22 uF [T491D226M010AT]
22 pF [CA064C220K4GAC TU]	22 uF [C1206C226K9PACT U]	22 uF [T491A226M006AT]	22 uF [T491D226M016AT]
22 pF [CA064C220K5GAC TU]	22 uF [C1206C226M9VAC TU]	22 uF [T491A226M010AT]	22 uF [T491D226M020AT]
22 pF [CA064C220K8GAC TU]	22 uF [C1210C226K4PACT U]	22 uF [T491B226M004AT]	22 uF [T491D226M025AT]
22 uF [A700D226M016AT E018]	22 uF [C1210C226K8PACT U]	22 uF [T491B226M006AT]	22 uF [T491D226M035AT]
22 uF [A700V226M006AT E028]	22 uF [C1210C226K8RACT U]	22 uF [T491B226M010AT]	22 uF [T491S226M004AT]
		22 uF [T491B226M016AT]	
		22 uF [T491B226M020AT]	22 uF [T491T226M004AT]

Multisim 14.0 Base Components

22 uF [T491T226M006AT]	22 uF [T494B226M006AT]	22 uF [T494D226M035AT]	22 uF [T495C226M025AT E900]
22 uF [T491T226M010AT]	22 uF [T494B226M010AT]	22 uF [T494S226M004AT]	22 uF [T495D226M020AT E180]
22 uF [T491U226M006AT]	22 uF [T494B226M016AT]	22 uF [T494T226M004AT]	22 uF [T495D226M020AT E225]
22 uF [T491U226M010AT]	22 uF [T494B226M020AT]	22 uF [T494T226M006AT]	22 uF [T495D226M025AT E200]
22 uF [T491U226M016AT]	22 uF [T494C226M004AT]	22 uF [T494T226M010AT]	22 uF [T495D226M035AT E125]
22 uF [T491V226M020AT]	22 uF [T494C226M006AT]	22 uF [T494U226M006AT]	22 uF [T495D226M035AT E200]
22 uF [T491V226M025AT]	22 uF [T494C226M010AT]	22 uF [T494U226M010AT]	22 uF [T495D226M035AT E200]
22 uF [T491X226M035AT]	22 uF [T494C226M016AT]	22 uF [T494U226M016AT]	22 uF [T495D226M035AT E300]
22 uF [T491X226M050AT]	22 uF [T494C226M020AT]	22 uF [T494U226M016AT]	22 uF [T495D226M035AT E300]
22 uF [T493X226M025AH 6110]	22 uF [T494C226M025AT]	22 uF [T494V226M020AT]	22 uF [T495X226M025AT E225]
22 uF [T494A226M004AT]	22 uF [T494D226M010AT]	22 uF [T494V226M025AT]	22 uF [T495X226M025AT E225]
22 uF [T494A226M006AT]	22 uF [T494D226M016AT]	22 uF [T494X226M035AT]	22 uF [T495X226M035AT E125]
22 uF [T494A226M010AT]	22 uF [T494D226M020AT]	22 uF [T494X226M050AT]	22 uF [T495X226M035AT E200]
22 uF [T494B226M004AT]	22 uF [T494D226M025AT]	22 uF [T495C226M025AT E300]	22 uF [T495X226M035AT E275]

Multisim 14.0 Base Components

22 uF [T497D226M006AT 6110]	22 uF [T520A226M006AT E090]	220 nF [C0603C224K3RACT U]	220 nF [C0805C224K8RACT U]
22 uF [T498B226M010AT E1K5]	22 uF [T520A226M006AT E100]	220 nF [C0603C224K4RACT U]	220 nF [C0805C224M3VAC TU]
22 uF [T498C226M006AT E1K3]	22 uF [T520A226M010AT E080]	220 nF [C0603C224K8NAC TU]	220 nF [C0805C224M4VAC TU]
22 uF [T498C226M010AT E1K1]	22 uF [T520C226M016AT E080]	220 nF [C0603C224K8RACT U]	220 nF [C1206C224K1RACT U]
22 uF [T498C226M016AT E1K0]	22 uF [T520T226M008AT E070]	220 nF [C0603C224K9RACT U]	220 nF [C1206C224K3RACT U]
22 uF [T498D226M025AT E600]	22 uF [T520V226M020AT E045]	220 nF [C0603C224M3VAC TU]	220 nF [C1206C224K4RACT U]
22 uF [T498X226M035AT E500]	22 uF [T520V226M020AT E090]	220 nF [C0603C224M4VAC TU]	220 nF [C1206C224K5RACT U]
22 uF [T499D226M016AT E800]	22 uF [T521V226M025AT E060]	220 nF [C0603C224M8VAC TU]	220 nF [C1206C224M5UAC TU]
22 uF [T510X226M035AT E060]	22 uF [T525B226M010AT E080]	220 nF [C0805C224K3RACT U]	220 nF [C1206F224K3RACT U]
22 uF [T510X226M035AT E080]	22 uF [T541X226M050AH 6510]	220 nF [C0805C224K4RACT U]	220 nF [C1206F224K4RACT U]
22 uF [T510X226M035AT E100]	220 nF [C0402C224K9PACT U]	220 nF [C0805C224K5RACT U]	220 nF [C1206F224K5RACT U]

Multisim 14.0 Base Components

220 nF [C1210C224K1RACT U]	220 nF [C1812C224K5RACT U]	220 nF [C1825C224M5UAC TU]	220 pF [C0402C221K1HACT U]
220 nF [C1210C224K3GACT U]	220 nF [C1812C224KARACT U]	220 nF [C2220C224K1GACT U]	220 pF [C0402C221K3HACT U]
220 nF [C1210C224K3RACT U]	220 nF [C1812C224M5UAC TU]	220 nF [C2220C224K5GACT U]	220 pF [C0402C221K3RACT U]
220 nF [C1210C224K5RACT U]	220 nF [C1812F224K1RACT U]	220 nF [C2225C224K1RACT U]	220 pF [C0402C221K4RACT U]
220 nF [C1210C224M5UAC TU]	220 nF [C1812F224K2RACT U]	220 nF [C2225C224K5RACT U]	220 pF [C0402C221K5GACT U]
220 nF [C1210F224K1RACT U]	220 nF [C1812F224K3RACT U]	220 nF [T409A224M035AH 4250]	220 pF [C0402C221K5HACT U]
220 nF [C1210F224K3RACT U]	220 nF [C1812F224K5RACT U]	220 nF [T491A224M035AT]	220 pF [C0402C221K5RACT U]
220 nF [C1210F224K4RACT U]	220 nF [C1825C224K1RACT U]	220 nF [T491B224M050AT]	220 pF [C0402C221K8RACT U]
220 nF [C1210F224K5RACT U]	220 nF [C1825C224K2RACT U]	220 nF [T493B224M050AH 6120]	220 pF [C0603C221K1RACT U]
220 nF [C1812C224K1RACT U]	220 nF [C1825C224K5RACT U]	220 nF [T494A224M035AT]	220 pF [C0603C221K2RACT U]
220 nF [C1812C224K5HACT U]	220 nF [C1825C224M1UAC TU]	220 nF [T499A224M035AT E18K]	220 pF [C0603C221K3GACT U]

Multisim 14.0 Base Components

220 pF [C0603C221K3RACT U]	220 pF [C0805C221K3RACT U]	220 pF [C1206C221KDGAC TU]	220 uF [A700D227M004AT E009]
220 pF [C0603C221K4GACT U]	220 pF [C0805C221K4RACT U]	220 pF [C1210C221K1GACT U]	220 uF [A700V227M002AT E009]
220 pF [C0603C221K4RACT U]	220 pF [C0805C221K5GACT U]	220 pF [C1210C221KBGAC TU]	220 uF [A700X227M004AT E010]
220 pF [C0603C221K5GACT U]	220 pF [C0805C221K5RACT U]	220 pF [C1812C221KBGAC TU]	220 uF [A700X227M004AT E015]
220 pF [C0603C221K5RACT U]	220 pF [C0805C221K8RACT U]	220 pF [C1825C221KBGAC TU]	220 uF [A700X227M2R5AT E010]
220 pF [C0603C221K8RACT U]	220 pF [C0805C221KARACT U]	220 pF [C2220C221KBGAC TU]	220 uF [A700X227M2R5AT E015]
220 pF [C0805C221K1GACT U]	220 pF [C1206C221K1GACT U]	220 pF [C2225C221KBGAC TU]	220 uF [T419H227M004AH 4250]
220 pF [C0805C221K1RACT U]	220 pF [C1206C221K2GACT U]	220 pF [CA064C221K5GAC TU]	220 uF [T491B227M004AT]
220 pF [C0805C221K2GACT U]	220 pF [C1206C221K5GACT U]	220 pF [CDR02BP221BKSM]	220 uF [T491C227M006AT]
220 pF [C0805C221K2RACT U]	220 pF [C1206C221KBGAC TU]	220 uF [A700D227M002AT E015]	220 uF [T491D227M006AT]
220 pF [C0805C221K3GACT U]	220 pF [C1206C221KCGAC TU]	220 uF [A700D227M002AT E018]	220 uF [T491D227M010AT]
			220 uF [T491D227M2R5AT]

Multisim 14.0 Base Components

220 uF [T491E227M016AT]	220 uF [T494X227M006AT]	220 uF [T495D227M010AT E125]	220 uF [T495X227M016AT E100]
220 uF [T491V227M004AT]	220 uF [T494X227M010AT]	220 uF [T495D227M2R5AT E045]	220 uF [T496X227M010AT 6110]
220 uF [T491V227M006AT]	220 uF [T494X227M016AT]	220 uF [T495E227M016AT E050]	220 uF [T498X227M010AT E500]
220 uF [T491X227M006AT]	220 uF [T495C227M006AT E225]	220 uF [T495E227M016AT E075]	220 uF [T510X227M016AT E025]
220 uF [T491X227M010AT]	220 uF [T495D227M004AT E040]	220 uF [T495E227M016AT E150]	220 uF [T510X227M016AT E040]
220 uF [T491X227M016AT]	220 uF [T495D227M004AT E050]	220 uF [T495X227M006AT E100]	220 uF [T513X227M016AH 6110]
220 uF [T494B227M004AT]	220 uF [T495D227M004AT E100]	220 uF [T495X227M010AT E045]	220 uF [T513X227M016AH 6120]
220 uF [T494C227M006AT]	220 uF [T495D227M006AT E045]	220 uF [T495X227M010AT E050]	220 uF [T520B227M004AT E035]
220 uF [T494D227M006AT]	220 uF [T495D227M006AT E100]	220 uF [T495X227M010AT E060]	220 uF [T520B227M004AT E045]
220 uF [T494D227M010AT]	220 uF [T495D227M010AT E045]	220 uF [T495X227M010AT E070]	220 uF [T520B227M006AT E035]
220 uF [T494D227M2R5AT]	220 uF [T495D227M010AT E100]		
220 uF [T494E227M016AT]			
220 uF [T494V227M004AT]			
220 uF [T494V227M006AT]			

Multisim 14.0 Base Components

220 uF [T520B227M2R5AT E015]	220 uF [T520C227M006AT E045]	220 uF [T520D227M010AT E025]	220 uF [T520V227M004AT E025]
220 uF [T520B227M2R5AT E018]	220 uF [T520C227M2R5AT E025]	220 uF [T520D227M010AT E040]	220 uF [T520V227M004AT E040]
220 uF [T520B227M2R5AT E025]	220 uF [T520D227M004AT E012]	220 uF [T520D227M2R5AT E007]	220 uF [T520V227M004AT E045]
220 uF [T520B227M2R5AT E030]	220 uF [T520D227M004AT E065]	220 uF [T520D227M2R5AT E040]	220 uF [T520V227M006AT E007]
220 uF [T520B227M2R5AT E035]	220 uF [T520D227M006AT E006]	220 uF [T520U227M2R5AT E055]	220 uF [T520V227M006AT E009]
220 uF [T520B227M2R5AT E070]	220 uF [T520D227M006AT E007]	220 uF [T520V227M004AT E006]	220 uF [T520V227M006AT E012]
220 uF [T520C227M004AT E018]	220 uF [T520D227M006AT E009]	220 uF [T520V227M004AT E007]	220 uF [T520V227M006AT E015]
220 uF [T520C227M004AT E025]	220 uF [T520D227M006AT E015]	220 uF [T520V227M004AT E009]	220 uF [T520V227M006AT E018]
220 uF [T520C227M004AT E045]	220 uF [T520D227M006AT E040]	220 uF [T520V227M004AT E012]	220 uF [T520V227M006AT E025]
220 uF [T520C227M004AT E055]	220 uF [T520D227M006AT E050]	220 uF [T520V227M004AT E015]	220 uF [T520V227M006AT E040]
220 uF [T520C227M006AT E025]	220 uF [T520D227M010AT E018]	220 uF [T520V227M004AT E018]	220 uF [T520V227M010AT E045]

Multisim 14.0 Base Components

220 uF [T520V227M2R5AT E007]	220 uF [T525D227M004AT E025]	220 uF [T530D227M010AT E010]	24 pF [C1812C240KBGAC TU]
220 uF [T520V227M2R5AT E009]	220 uF [T525D227M006AT E025]	220 uF [T530Y227M010AT E006]	24 pF [C1825C240KBGAC TU]
220 uF [T520V227M2R5AT E012]	220 uF [T525D227M010AT E025]	220 uF [T541D227M010AH 6510]	24 pF [C1825C240KCGAC TU]
220 uF [T520V227M2R5AT E015]	220 uF [T528Z227M004AT E007]	220 uF [T543V227M004AT E015]	24 pF [C2220C240KBGAC TU]
220 uF [T520V227M2R5AT E025]	220 uF [T528Z227M004AT E009]	24 pF [C0402C240K4GACT U]	24 pF [C2225C240KBGAC TU]
220 uF [T520V227M2R5AT E045]	220 uF [T528Z227M004AT E012]	24 pF [C0402C240K5GACT U]	240 pF [C0402C241K1HACT U]
220 uF [T520W227M004AT E025]	220 uF [T528Z227M006AT E009]	24 pF [C0603C240K2GACT U]	240 pF [C0402C241K3HACT U]
220 uF [T520W227M004AT E040]	220 uF [T528Z227M006AT E012]	24 pF [C0805C240K5GACT U]	240 pF [C0402C241K5HACT U]
220 uF [T520Y227M010AT E040]	220 uF [T530D227M006AT E005]	24 pF [C0805C240KBGAC TU]	240 pF [C0603C241K5GACT U]
220 uF [T522V227M006AT E025]	220 uF [T530D227M006AT E006]	24 pF [C1206C240KBGAC TU]	240 pF [C0805C241K5GACT U]
220 uF [T522V227M006AT E040]	220 uF [T530D227M010AT E006]	24 pF [C1210C240KBGAC TU]	240 pF [C1206C241KBGAC TU]

Multisim 14.0 Base Components

240 pF [C1210C241KBGAC TU]	27 nF [C0402C273K8RACT U]	27 nF [C0805C273K4RACT U]	27 nF [C1206C273K5HACT U]
240 pF [C1812C241KBGAC TU]	27 nF [C0402C273K9PACT U]	27 nF [C0805C273K5RACT U]	27 nF [C1206C273K5RACT U]
240 pF [C1825C241KBGAC TU]	27 nF [C0402C273K9RACT U]	27 nF [C0805C273K8RACT U]	27 nF [C1206C273KARACT U]
240 pF [C2220C241KBGAC TU]	27 nF [C0603C273K1RACT U]	27 nF [C0805C273M5UAC TU]	27 nF [C1210C273K1GACT U]
240 pF [C2225C241KBGAC TU]	27 nF [C0603C273K3RACT U]	27 nF [C0805F273K1RACT U]	27 nF [C1210C273K1HACT U]
25_AMP 2-534206-0	27 nF [C0603C273K4RACT U]	27 nF [C0805F273K3RACT U]	27 nF [C1210C273K1RACT U]
27 mF [C0402C279K5GACT U]	27 nF [C0603C273K5RACT U]	27 nF [C0805F273K4RACT U]	27 nF [C1210C273K2RACT U]
27 mF [C0805C279KBGAC TU]	27 nF [C0805C273K1RACT U]	27 nF [C0805F273K5RACT U]	27 nF [C1210C273K3GACT U]
27 nF [C0402C273K3RACT U]	27 nF [C0805C273K2RACT U]	27 nF [C1206C273K1HACT U]	27 nF [C1210C273K3HACT U]
27 nF [C0402C273K4RACT U]	27 nF [C0805C273K3HACT U]	27 nF [C1206C273K1RACT U]	27 nF [C1210C273K5GACT U]
27 nF [C0402C273K8PACT U]	27 nF [C0805C273K3RACT U]	27 nF [C1206C273K3HACT U]	27 nF [C1210C273K5HACT U]

Multisim 14.0 Base Components

27 nF [C1210C273K5RACT U]	27 pF [C0402C270K4GACT U]	27 pF [C1206C270K1GACT U]	27 pF [CA064C270K8GAC TU]
27 nF [C1210C273KARACT U]	27 pF [C0402C270K5GACT U]	27 pF [C1206C270K2GACT U]	270 nF [C0603C274K4PACT U]
27 nF [C1812C273K1HACT U]	27 pF [C0402C270K8GACT U]	27 pF [C1206C270K5GACT U]	270 nF [C0603C274K4RACT U]
27 nF [C1812C273K1RACT U]	27 pF [C0603C270K1GACT U]	27 pF [C1206C270KBGAC TU]	270 nF [C0603C274K8PACT U]
27 nF [C1812C273K5HACT U]	27 pF [C0603C270K2GACT U]	27 pF [C1210C270KBGAC TU]	270 nF [C0603C274K8RACT U]
27 nF [C1825C273K1GACT U]	27 pF [C0603C270K5GACT U]	27 pF [C1812C270KBGAC TU]	270 nF [C0603C274K9PACT U]
27 nF [C1825C273K5GACT U]	27 pF [C0805C270K1GACT U]	27 pF [C1812C270KHGAC TU]	270 nF [C0603C274K9RACT U]
27 nF [C2220C273K1GACT U]	27 pF [C0805C270K2GACT U]	27 pF [C1825C270KBGAC TU]	270 nF [C0805C274K3RACT U]
27 nF [C2220C273K2GACT U]	27 pF [C0805C270K5GACT U]	27 pF [C2220C270KBGAC TU]	270 nF [C0805C274K4RACT U]
27 pF [C0201C270K3GACT U]	27 pF [C0805C270KBGAC TU]	27 pF [C2225C270KBGAC TU]	270 nF [C0805C274K8RACT U]
27 pF [C0402C270K3GACT U]	27 pF [C0805C270KDGAC TU]	27 pF [CA064C270K5GAC TU]	270 nF [C1206C274K1RACT U]

Multisim 14.0 Base Components

270 nF [C1206C274K3RACT U]	270 nF [C1210F274K3RACT U]	270 nF [C1825C274K5RACT U]	270 pF [C0402C271K5GACT U]
270 nF [C1206C274K4RACT U]	270 nF [C1210F274K4RACT U]	270 nF [C2220C274K1GACT U]	270 pF [C0402C271K5HACT U]
270 nF [C1206C274K5RACT U]	270 nF [C1210F274K5RACT U]	270 nF [C2220C274K5GACT U]	270 pF [C0402C271K5RACT U]
270 nF [C1206F274K3RACT U]	270 nF [C1812C274K1RACT U]	270 nF [C2220C274K5RACT U]	270 pF [C0402C271K8RACT U]
270 nF [C1206F274K4RACT U]	270 nF [C1812C274K5RACT U]	270 nF [C2225C274K1RACT U]	270 pF [C0603C271K1RACT U]
270 nF [C1206F274K5RACT U]	270 nF [C1812C274KARACT U]	270 nF [C2225C274K2RACT U]	270 pF [C0603C271K2RACT U]
270 nF [C1210C274K1RACT U]	270 nF [C1812F274K1RACT U]	270 nF [C2225C274K5RACT U]	270 pF [C0603C271K3RACT U]
270 nF [C1210C274K3RACT U]	270 nF [C1812F274K2RACT U]	270 pF [C0402C271K1HACT U]	270 pF [C0603C271K4GACT U]
270 nF [C1210C274K5RACT U]	270 nF [C1812F274K3RACT U]	270 pF [C0402C271K3HACT U]	270 pF [C0603C271K4RACT U]
270 nF [C1210C274M5UAC TU]	270 nF [C1812F274K5RACT U]	270 pF [C0402C271K3RACT U]	270 pF [C0603C271K5GACT U]
270 nF [C1210F274K1RACT U]	270 nF [C1825C274K1RACT U]	270 pF [C0402C271K4RACT U]	270 pF [C0603C271K5RACT U]

Multisim 14.0 Base Components

270 pF [C0805C271K1GACT U]	270 pF [C1210C271KBGAC TU]	292303-1	2N3391
		292304-1	2N3391A
270 pF [C0805C271K1RACT U]	270 pF [C1812C271KBGAC TU]	2A3	2N3392
		2K8RAM	2N3393
270 pF [C0805C271K2GACT U]	270 pF [C1825C271KBGAC TU]	2N1599	2N3394
		2N2222A	2N3414
270 pF [C0805C271K2RACT U]	270 pF [C2220C271KBGAC TU]	2N2573	2N3415
		2N2574	2N3416
270 pF [C0805C271K4RACT U]	270 pF [C2225C271KBGAC TU]	2N2575	2N3417
		2N2576	2N3442G
270 pF [C0805C271K5GACT U]	270 pF [C2225C271KBGAC TU]	2N2577	2N3458
		2N2578	2N3459
270 pF [C0805C271K5RACT U]	270 uF [A700X277M002AT E010]	2N2579	2N3668
		2N2608	2N3669
270 pF [C0805C271K5RACT U]	270 uF [A700X277M002AT E015]	2N2609	2N3670
		2N2712	2N3684
270 pF [C1206C271K1GACT U]	270 uF [A700X277M004AT E010]	2N2714	2N3685
		2N2923	2N3686
270 pF [C1206C271K2GACT U]	270 uF [A700X277M004AT E015]	2N2924	2N3687
		2N2925	2N3702
270 pF [C1206C271K5GACT U]	282834-2	2N3055A	2N3703
	282834-4	2N3055AG	2N3707
270 pF [C1206C271KBGAC TU]	282834-5	2N3055G	2N3711
	282834-8	2N3370	2N3771G
	28V_7.5W	2N3390	2N3772G

Multisim 14.0 Base Components

2N3773G	2N3954	2N4126	2N4221
2N3821	2N3954A	2N4167	2N4221A
2N3822	2N3955	2N4168	2N4222
2N3823	2N3955A	2N4169	2N4222A
2N3824	2N3956	2N4170	2N4223
2N3858A	2N3957	2N4171	2N4286
2N3859	2N3958	2N4172	2N4289
2N3859A	2N3966	2N4173	2N4291
2N3860	2N3967	2N4174	2N4338
2N3870	2N3970	2N4183	2N4339
2N3871	2N3971	2N4184	2N4340
2N3872	2N3972	2N4185	2N4341
2N3873	2N4058	2N4186	2N4381
2N3896	2N4061	2N4187	2N4391
2N3897	2N4062	2N4188	2N4392
2N3898	2N4084	2N4189	2N4393
2N3899	2N4091	2N4190	2N4400
2N3903	2N4092	2N4199	2N4401
2N3904	2N4093	2N4200	2N4402
2N3904G	2N4117A	2N4201	2N4403
2N3905	2N4118A	2N4202	2N4409
2N3906	2N4119A	2N4203	2N4410
2N3906G	2N4123	2N4204	2N4416
2N3921	2N4124	2N4220	2N4416A
2N3922	2N4125	2N4220A	2N4424

Multisim 14.0 Base Components

2N4441	2N5021	2N5191G	2N5432
2N4442	2N5038G	2N5192G	2N5433
2N4443	2N5045	2N5194G	2N5434
2N4444	2N5046	2N5195G	2N5444
2N4856	2N5047	2N5196	2N5445
2N4856A	2N5060	2N5197	2N5446
2N4857	2N5061	2N5199	2N5447
2N4857A	2N5062	2N5209	2N5452
2N4858	2N5063	2N5210	2N5454
2N4858A	2N5064	2N5223	2N5484
2N4859	2N5078	2N5224	2N5485
2N4859A	2N5086	2N5226	2N5486
2N4860	2N5087	2N5227	2N5515
2N4860A	2N5088	2N5232	2N5516
2N4861	2N5089	2N5232A	2N5517
2N4861A	2N5103	2N5302G	2N5518
2N4918G	2N5105	2N5354	2N5519
2N4919G	2N5114	2N5355	2N5520
2N4920G	2N5115	2N5358	2N5521
2N4921G	2N5116	2N5365	2N5522
2N4922G	2N5168	2N5366	2N5523
2N4923G	2N5169	2N5397	2N5524
2N5018	2N5170	2N5398	2N5545
2N5019	2N5171	2N5400	2N5550
2N5020	2N5172	2N5401	2N5550G

Multisim 14.0 Base Components

2N5550RLRPG	2N6027G	2N6147	2N6342
2N5551	2N6027RL1G	2N6157	2N6343
2N5556	2N6027RLRAG	2N6158	2N6344
2N5557	2N6028	2N6159	2N6345
2N5558	2N6028G	2N6160	2N6346
2N5564	2N6028RLRAG	2N6161	2N6347
2N5565	2N6028RLRMG	2N6162	2N6348
2N5566	2N6028RLRPG	2N6163	2N6349
2N5567	2N6034G	2N6164	2N6387G
2N5568	2N6035G	2N6165	2N6388G
2N5571	2N6036G	2N6167	2N6394
2N5572	2N6038G	2N6168	2N6395
2N5655G	2N6039G	2N6169	2N6396
2N5657G	2N6040G	2N6170	2N6397
2N5684G	2N6042G	2N6171	2N6398
2N5686G	2N6043G	2N6172	2N6399
2N5769	2N6045G	2N6173	2N6400
2N5771	2N6052G	2N6174	2N6401
2N5817	2N6071	2N6284G	2N6402
2N5830	2N6073BG	2N6286G	2N6403
2N5883G	2N6107G	2N6287G	2N6404
2N5884G	2N6109G	2N6288G	2N6405
2N5885G	2N6111G	2N6292G	2N6487G
2N5886G	2N6145	2N6338G	2N6488G
2N6027	2N6146	2N6341G	2N6490G

Multisim 14.0 Base Components

2N6491G	2N7002PT	2PB709ASW	2PD602ARL
2N6667G	2N7002PV	2PB709BRL	2PD602ASL
2N6715	2N7002PW	2PB709BSL	2SA1015
2N6727	2P1S	2PB710ARL	2SA1020
2N7000	2P2S	2PB710ASL	2SA1213
2N7000G	2PA1576Q	2PC4081Q	2SA1416S-TD-E
2N7000RLRAG	2PA1576R	2PC4081R	2SA1416T-TD-E
2N7002	2PA1576S	2PC4081S	2SA1460
2N7002BK	2PA1774Q	2PC4617Q	2SA1507S
2N7002BKM	2PA1774QM	2PC4617QM	2SA1507T
2N7002BKMB	2PA1774QMB	2PC4617QMB	2SA1774G
2N7002BKS	2PA1774R	2PC4617R	2SA1774T1G
2N7002BKT	2PA1774RM	2PC4617RM	2SA2126-E
2N7002BKV	2PA1774RMB	2PC4617RMB	2SA2126-H
2N7002BKW	2PA1774S	2PD1820AR	2SA2126-TL-E
2N7002CK	2PA1774SM	2PD1820AS	2SA2126-TL-H
2N7002DW	2PA1774SMB	2PD2150	2SA2205-E
2N7002E	2PB1219AQ	2PD601ARL	2SA2205-TL-E
2N7002ET1G	2PB1219AR	2PD601ART	2SA733
2N7002F	2PB1219AS	2PD601ARW	2SA952
2N7002K	2PB1424	2PD601ASL	2SA953
2N7002LT1G	2PB709ARL	2PD601ASW	2SA954
2N7002LT3G	2PB709ART	2PD601BRL	2SB1205S-TL-E
2N7002P	2PB709ARW	2PD601BSL	2SB1205T-TL-E
2N7002PS	2PB709ASL	2PD602AQL	2SC1815

Multisim 14.0 Base Components

2SC2001	2SD1628F-TD-H	2SK3069	2SK3748-1E
2SC2120	2SD1628G-TD-E	2SK3070L	2SK3820-DL-E
2SC2240	2SD1628G-TD-H	2SK3070S	2SK3820-E
2SC2655	2SD1805F-E	2SK30ATM	2V7002LT1G
2SC2786	2SD1805F-TL-E	2SK3133	2V7002LT3G
2SC2873	2SD1805G-E	2SK3134	3 nF
2SC3649S-TD-E	2SD1805G-TL-E	2SK3135	[C0603C302K1HACT U]
2SC3649S-TD-H	2SD1815S-E	2SK3136	3 nF
2SC3649T-TD-E	2SD1815S-TL-E	2SK3140	[C0603C302K3HACT U]
2SC3649T-TD-H	2SD1815T-E	2SK3141	3 nF
2SC3733	2SD1815T-TL-E	2SK3142	[C0603C302K5HACT U]
2SC4617G	2SJ517	2SK3203	3 nF
2SC4617T1G	2SJ652	2SK3233	[C0805C302K1GACT U]
2SC5566-TD-E	2SJ652-RA11	2SK330	3 nF
2SC5658M3T5G	2SJ661-E	2SK364	[C0805C302K1HACT U]
2SC5706-E	2SJ665-DL-E	2SK366	3 nF
2SC5706-H	2SK117	2SK367	[C0805C302K3GACT U]
2SC5706-TL-E	2SK170	2SK368	3 nF
2SC5706-TL-H	2SK192A	2SK3703	[C0805C302K3HACT U]
2SC5964-TD-E	2SK208	2SK3704	3 nF
2SC5964-TD-H	2SK209	2SK3746	[C0805C302K5HACT U]
2SC945	2SK2553L	2SK3746-1E	3 nF
2SD1623S-TD-E	2SK2553S	2SK3747	[C1825C302KBGAC TU]
2SD1623T-TD-E	2SK2978	2SK3747-1E	
2SD1628F-TD-E	2SK2980	2SK3748	

Multisim 14.0 Base Components

3 nF [C2220C302KBGAC TU]	3.3 nF [C0603C332K3RACT U]	3.3 nF [C0805C332K4RACT U]	3.3 nF [C1206C332K5RACT U]
3 nF [C2225C302KBGAC TU]	3.3 nF [C0603C332K4RACT U]	3.3 nF [C0805C332K5GACT U]	3.3 nF [C1210C332K1RACT U]
3.3 nF [C0402C332K3RACT U]	3.3 nF [C0603C332K5HACT U]	3.3 nF [C0805C332K5HACT U]	3.3 nF [C1210C332K2GACT U]
3.3 nF [C0402C332K4RACT U]	3.3 nF [C0603C332K5RACT U]	3.3 nF [C0805C332K5RACT U]	3.3 nF [C1210C332K5GACT U]
3.3 nF [C0402C332K5RACT U]	3.3 nF [C0805C332K1GACT U]	3.3 nF [C0805C332K8GACT U]	3.3 nF [C1210C332K5RACT U]
3.3 nF [C0402C332K8RACT U]	3.3 nF [C0805C332K1HACT U]	3.3 nF [C0805C332KARACT U]	3.3 nF [C1825C332KBGAC TU]
3.3 nF [C0402C332K9RACT U]	3.3 nF [C0805C332K1RACT U]	3.3 nF [C1206C332K1GACT U]	3.3 nF [C2220C332KBGAC TU]
3.3 nF [C0603C332K1HACT U]	3.3 nF [C0805C332K2RACT U]	3.3 nF [C1206C332K1RACT U]	3.3 nF [C2225C332KBGAC TU]
3.3 nF [C0603C332K1RACT U]	3.3 nF [C0805C332K3GACT U]	3.3 nF [C1206C332K2RACT U]	3.3 nF [CA064C332K1RACT U]
3.3 nF [C0603C332K3GACT U]	3.3 nF [C0805C332K3HACT U]	3.3 nF [C1206C332K3RACT U]	3.3 nF [CA064C332K5RACT U]
3.3 nF [C0603C332K3HACT U]	3.3 nF [C0805C332K4GACT U]	3.3 nF [C1206C332K5GACT U]	3.3 uF [C0805C335K4PACT U]

Multisim 14.0 Base Components

3.3 uF [C0805C335K8PACT U]	3.3 uF [C1210C335K3PACT U]	3.3 uF [T491B335M025AT]	3.3 uF [T494B335M016AT]
3.3 uF [C0805C335K9PACT U]	3.3 uF [C1210C335K4PACT U]	3.3 uF [T491B335M035AT]	3.3 uF [T494B335M020AT]
3.3 uF [C1206C335K3PACT U]	3.3 uF [C1210C335K4RACT U]	3.3 uF [T491C335M025AT]	3.3 uF [T494B335M025AT]
3.3 uF [C1206C335K4PACT U]	3.3 uF [C1210C335K8PACT U]	3.3 uF [T491D335M035AT]	3.3 uF [T494C335M025AT]
3.3 uF [C1206C335K4RACT U]	3.3 uF [T409B335M006AH 4250]	3.3 uF [T491D335M050AT]	3.3 uF [T494C335M035AT]
3.3 uF [C1206C335K8PACT U]	3.3 uF [T489A335M020AT E3K7]	3.3 uF [T491S335M010AT]	3.3 uF [T494D335M050AT]
3.3 uF [C1206C335K8RACT U]	3.3 uF [T491A335M004AT]	3.3 uF [T491T335M020AT]	3.3 uF [T494S335M010AT]
3.3 uF [C1206C335K9PACT U]	3.3 uF [T491A335M006AT]	3.3 uF [T493A335M004AH 6110]	3.3 uF [T494T335M020AT]
3.3 uF [C1206C335K9RACT U]	3.3 uF [T491A335M010AT]	3.3 uF [T494A335M004AT]	3.3 uF [T495A335M016AT E3K0]
3.3 uF [C1206C335M4VAC TU]	3.3 uF [T491A335M020AT]	3.3 uF [T494A335M006AT]	3.3 uF [T495B335M035AT E900]
3.3 uF [C1206C335M9VAC TU]	3.3 uF [T491B335M016AT]	3.3 uF [T494A335M010AT]	3.3 uF [T495C335M035AT E525]
	3.3 uF [T491B335M020AT]	3.3 uF [T494A335M016AT]	3.3 uF [T495C335M035AT E550]

Multisim 14.0 Base Components

3.3 uF [T495C335M035AT E600]	3.6 nF [C1825C362KBGAC TU]	3.9 nF [C0603C392K4RACT U]	3.9 nF [C0805C392K4RACT U]
3.3 uF [T498A335M010AT E3K6]	3.6 nF [C2220C362KBGAC TU]	3.9 nF [C0603C392K5HACT U]	3.9 nF [C0805C392K5GACT U]
3.3 uF [T498A335M016AT E3K4]	3.6 nF [C2225C362KBGAC TU]	3.9 nF [C0603C392K5RACT U]	3.9 nF [C0805C392K5HACT U]
3.3 uF [T498C335M035AT E1K7]	3.9 nF [C0402C392K3RACT U]	3.9 nF [C0805C392K1GACT U]	3.9 nF [C0805C392K5RACT U]
3.6 nF [C0603C362K1HACT U]	3.9 nF [C0402C392K4RACT U]	3.9 nF [C0805C392K1HACT U]	3.9 nF [C0805C392KARACT U]
3.6 nF [C0603C362K3HACT U]	3.9 nF [C0402C392K5RACT U]	3.9 nF [C0805C392K1RACT U]	3.9 nF [C1206C392K1GACT U]
3.6 nF [C0603C362K5HACT U]	3.9 nF [C0603C392K1HACT U]	3.9 nF [C0805C392K2RACT U]	3.9 nF [C1206C392K1RACT U]
3.6 nF [C0805C362K1GACT U]	3.9 nF [C0603C392K1RACT U]	3.9 nF [C0805C392K3GACT U]	3.9 nF [C1206C392K2RACT U]
3.6 nF [C0805C362K1HACT U]	3.9 nF [C0603C392K3GACT U]	3.9 nF [C0805C392K3HACT U]	3.9 nF [C1206C392K5GACT U]
3.6 nF [C0805C362K3HACT U]	3.9 nF [C0603C392K3HACT U]	3.9 nF [C0805C392K3RACT U]	3.9 nF [C1206C392K5RACT U]
3.6 nF [C0805C362K5HACT U]	3.9 nF [C0603C392K3RACT U]	3.9 nF [C0805C392K4GACT U]	3.9 nF [C1210C392K5RACT U]

Multisim 14.0 Base Components

3.9 nF [C1812C392K2GACT U]	30 mF [C0805C309KBGAC TU]	30 pF [C1812C300KBGAC TU]	300 pF [C1206C301KBGAC TU]
3.9 nF [C1825C392KBGAC TU]	30 pF [C0402C300K5GACT U]	30 pF [C1825C300KBGAC TU]	300 pF [C1210C301KBGAC TU]
3.9 nF [C2220C392KBGAC TU]	30 pF [C0603C300K2GACT U]	30 pF [C2220C300KBGAC TU]	300 pF [C1812C301KBGAC TU]
3.9 nF [C2225C392KBGAC TU]	30 pF [C0603C300K5GACT U]	30 pF [C2225C300KBGAC TU]	300 pF [C1825C301KBGAC TU]
3.9 nF [C2225C392KCGAC TU]	30 pF [C0805C300K2GACT U]	30_AMP 300 pF [C0402C301K1HACT U]	300 pF [C2220C301KBGAC TU]
3.9 nF [CDR02BX392BKSM]	30 pF [C0805C300K5GACT U]	300 pF [C0402C301K3HACT U]	300 pF [C2225C301KBGAC TU]
3.9 uF [C1206C395K4RACT U]	30 pF [C0805C300KBGAC TU]	300 pF [C0402C301K5HACT U]	30V_10W
3.9 uF [C1206C395K8RACT U]	30 pF [C1206C300K1GACT U]	300 pF [C0805C301K1GACT U]	3280A
3.9 uF [C1206C395K9RACT U]	30 pF [C1206C300K5GACT U]	300 pF [C0805C301K2GACT U]	3288RT
3.9 uF [C1210C395K3NAC TU]	30 pF [C1206C300KBGAC TU]	300 pF [C0805C301K5GACT U]	33 mF [C0805C339KBGAC TU]
3_AMP	30 pF [C1210C300KBGAC TU]	300 pF [C1206C301K5GACT U]	33 mF [C1206C339K5GACT U]
30 mF [C0402C309K5GACT U]		300 pF [C1206C301K5GACT U]	33 nF [C0402C333K3RACT U]
			33 nF [C0402C333K4RACT U]

Multisim 14.0 Base Components

33 nF [C0402C333K8PACT U]	33 nF [C0805C333K2RACT U]	33 nF [C0805F333K5RACT U]	33 nF [C1210C333K1GACT U]
33 nF [C0402C333K8RACT U]	33 nF [C0805C333K3GACT U]	33 nF [C1206C333K1HACT U]	33 nF [C1210C333K1HACT U]
33 nF [C0402C333K9PACT U]	33 nF [C0805C333K3HACT U]	33 nF [C1206C333K1RACT U]	33 nF [C1210C333K1RACT U]
33 nF [C0402C333K9RACT U]	33 nF [C0805C333K3RACT U]	33 nF [C1206C333K2RACT U]	33 nF [C1210C333K2RACT U]
33 nF [C0603C333K1RACT U]	33 nF [C0805C333K4RACT U]	33 nF [C1206C333K3GACT U]	33 nF [C1210C333K3GACT U]
33 nF [C0603C333K3RACT U]	33 nF [C0805C333K5RACT U]	33 nF [C1206C333K3HACT U]	33 nF [C1210C333K3HACT U]
33 nF [C0603C333K4RACT U]	33 nF [C0805C333K8RACT U]	33 nF [C1206C333K5HACT U]	33 nF [C1210C333K5GACT U]
33 nF [C0603C333K5RACT U]	33 nF [C0805C333M5UAC TU]	33 nF [C1206C333K5RACT U]	33 nF [C1210C333K5HACT U]
33 nF [C0603C333K8RACT U]	33 nF [C0805F333K1RACT U]	33 nF [C1206C333KARACT U]	33 nF [C1210C333K5RACT U]
33 nF [C0603C333M3VAC TU]	33 nF [C0805F333K3RACT U]	33 nF [C1206C333M1UAC TU]	33 nF [C1210C333KARACT U]
33 nF [C0805C333K1RACT U]	33 nF [C0805F333K4RACT U]	33 nF [C1206C333M5UAC TU]	33 nF [C1812C333K1GACT U]

Multisim 14.0 Base Components

33 nF [C1812C333K1HACT U]	33 nF [C2225C333K5GACT U]	33 pF [C0805C330K1GACT U]	33 pF [C1206C330KGGAC TU]
33 nF [C1812C333K1RACT U]	33 nF [CA064C333K4RACT U]	33 pF [C0805C330K2GACT U]	33 pF [C1210C330KBGAC TU]
33 nF [C1812C333K2RACT U]	33 pF [C0201C330K3GACT U]	33 pF [C0805C330K5GACT U]	33 pF [C1812C330KBGAC TU]
33 nF [C1812C333K5GACT U]	33 pF [C0402C330K3GACT U]	33 pF [C0805C330KBGAC TU]	33 pF [C1825C330KBGAC TU]
33 nF [C1812C333K5HACT U]	33 pF [C0402C330K4GACT U]	33 pF [C0805C330KDGAC TU]	33 pF [C2220C330KBGAC TU]
33 nF [C1812C333K5RACT U]	33 pF [C0402C330K5GACT U]	33 pF [C1206C330K1GACT U]	33 pF [C2225C330KBGAC TU]
33 nF [C1825C333K1RACT U]	33 pF [C0402C330K8GACT U]	33 pF [C1206C330K2GACT U]	33 pF [CA064C330K5GAC TU]
33 nF [C1825C333K5RACT U]	33 pF [C0603C330K1GACT U]	33 pF [C1206C330K5GACT U]	33 pF [CA064C330K8GAC TU]
33 nF [C2220C333K1GACT U]	33 pF [C0603C330K2GACT U]	33 pF [C1206C330KBGAC TU]	33 uF [A700V336M006AT E018]
33 nF [C2220C333K2GACT U]	33 pF [C0603C330K3GACT U]	33 pF [C1206C330KCGAC TU]	33 uF [A700V336M006AT E025]
33 nF [C2220C333K5GACT U]	33 pF [C0603C330K5GACT U]	33 pF [C1206C330KDGAC TU]	33 uF [A700V336M006AT E028]

Multisim 14.0 Base Components

33 uF [A700V336M008AT E018]	33 uF [T491A336M003AT]	33 uF [T491D336M016AT]	33 uF [T491V336M020AT]
33 uF [A700V336M008AT E025]	33 uF [T491A336M004AT]	33 uF [T491D336M020AT]	33 uF [T491X336M025AT]
33 uF [A700V336M008AT E028]	33 uF [T491A336M006AT]	33 uF [T491D336M025AT]	33 uF [T491X336M035AT]
33 uF [A700V336M010AT E018]	33 uF [T491B336M004AT]	33 uF [T491D336M035AT]	33 uF [T494A336M004AT]
33 uF [A700V336M010AT E025]	33 uF [T491B336M006AT]	33 uF [T491T336M004AT]	33 uF [T494A336M006AT]
33 uF [A700V336M010AT E028]	33 uF [T491B336M010AT]	33 uF [T491T336M006AT]	33 uF [T494A336M010AT]
33 uF [T409F336M004AH 4250]	33 uF [T491B336M016AT]	33 uF [T491T336M010AT]	33 uF [T494B336M004AT]
33 uF [T409G336M010AH 4250]	33 uF [T491C336M004AT]	33 uF [T491U336M004AT]	33 uF [T494B336M006AT]
33 uF [T419E336M006AH 4250]	33 uF [T491C336M006AT]	33 uF [T491U336M006AT]	33 uF [T494B336M010AT]
33 uF [T419X336M025AH 4250]	33 uF [T491C336M010AT]	33 uF [T491U336M010AT]	33 uF [T494C336M004AT]
33 uF [T489D336M020AT E250]	33 uF [T491C336M016AT]	33 uF [T491U336M016AT]	33 uF [T494C336M006AT]
	33 uF [T491C336M020AT]	33 uF [T491V336M010AT]	33 uF [T494C336M010AT]
	33 uF [T491C336M025AT]		33 uF [T494C336M016AT]
	33 uF [T491D336M010AT]		33 uF [T494C336M020AT]

Multisim 14.0 Base Components

33 uF [T494C336M025AT]	33 uF [T494U336M016AT]	33 uF [T495D336M025AT E100]	33 uF [T495X336M035AT E250]
33 uF [T494D336M010AT]	33 uF [T494V336M010AT]	33 uF [T495D336M025AT E225]	33 uF [T497H336M015AT 6110]
33 uF [T494D336M016AT]	33 uF [T494V336M020AT]	33 uF [T495D336M025AT E300]	33 uF [T498B336M006AT E1K7]
33 uF [T494D336M020AT]	33 uF [T494X336M025AT]	33 uF [T495E336M035AT E200]	33 uF [T498D336M016AT E600]
33 uF [T494D336M025AT]	33 uF [T495B336M010AT E450]	33 uF [T495V336M010AT E100]	33 uF [T498D336M025AT E600]
33 uF [T494D336M035AT]	33 uF [T495C336M016AT E200]	33 uF [T495V336M010AT E150]	33 uF [T498X336M035AT E500]
33 uF [T494T336M004AT]	33 uF [T495C336M016AT E275]	33 uF [T495X336M025AT E100]	33 uF [T510X336M035AT E050]
33 uF [T494T336M006AT]	33 uF [T495D336M016AT E225]	33 uF [T495X336M025AT E175]	33 uF [T510X336M035AT E065]
33 uF [T494U336M004AT]	33 uF [T495D336M020AT E100]	33 uF [T495X336M025AT E200]	33 uF [T520A336M004AT E070]
33 uF [T494U336M006AT]	33 uF [T495D336M020AT E200]	33 uF [T495X336M035AT E100]	33 uF [T520A336M004AT E080]
33 uF [T494U336M010AT]	33 uF [T495D336M025AT E090]	33 uF [T495X336M035AT E175]	33 uF [T520A336M006AT E070]

Multisim 14.0 Base Components

33 uF [T520A336M006AT E080]	33 uF [T520B336M010AT E070]	33 uF [T520V336M016AT E070]	33 uF [T543A336M004AT E070]
33 uF [T520B336M006AT E025]	33 uF [T520C336M006AT E100]	33 uF [T520W336M016AT E045]	33 uF [T543B336M010AT E040]
33 uF [T520B336M006AT E035]	33 uF [T520T336M006AT E070]	33 uF [T521D336M025AT E060]	330 nF [C0603C334K4PACT U]
33 uF [T520B336M006AT E040]	33 uF [T520T336M008AT E070]	33 uF [T521D336M035AT E065]	330 nF [C0603C334K4RACT U]
33 uF [T520B336M006AT E070]	33 uF [T520T336M008AT E080]	33 uF [T521V336M025AT E060]	330 nF [C0603C334K8PACT U]
33 uF [T520B336M008AT E025]	33 uF [T520T336M010AT E070]	33 uF [T525B336M006AT E080]	330 nF [C0603C334K8RACT U]
33 uF [T520B336M008AT E035]	33 uF [T520T336M010AT E080]	33 uF [T525B336M010AT E080]	330 nF [C0603C334K9RACT U]
33 uF [T520B336M008AT E040]	33 uF [T520U336M008AT E070]	33 uF [T525T336M008AT E080]	330 nF [C0805C334K3NAC TU]
33 uF [T520B336M008AT E070]	33 uF [T520U336M010AT E070]	33 uF [T525T336M010AT E080]	330 nF [C0805C334K3RACT U]
33 uF [T520B336M010AT E035]	33 uF [T520V336M016AT E045]	33 uF [T528I336M010ATE 150]	330 nF [C0805C334K4RACT U]
33 uF [T520B336M010AT E040]	33 uF [T520V336M016AT E060]	33 uF [T541X336M050AH 6510]	330 nF [C0805C334K8RACT U]

Multisim 14.0 Base Components

330 nF [C0805C334M3VAC TU]	330 nF [C1210C334K3RACT U]	330 nF [C1812C334M5UAC TU]	330 nF [C2220C334K2RACT U]
330 nF [C0805C334M4VAC TU]	330 nF [C1210C334K5RACT U]	330 nF [C1812F334K1RACT U]	330 nF [C2220C334K5GACT U]
330 nF [C0805C334M8VAC TU]	330 nF [C1210C334M5UAC TU]	330 nF [C1812F334K2RACT U]	330 nF [C2220C334K5RACT U]
330 nF [C1206C334K1RACT U]	330 nF [C1210C334M5VAC TU]	330 nF [C1812F334K3RACT U]	330 nF [C2225C334K1RACT U]
330 nF [C1206C334K3RACT U]	330 nF [C1210F334K1RACT U]	330 nF [C1812F334K5RACT U]	330 nF [C2225C334K2RACT U]
330 nF [C1206C334K4RACT U]	330 nF [C1210F334K3RACT U]	330 nF [C1825C334K1RACT U]	330 nF [C2225C334K5RACT U]
330 nF [C1206C334K5RACT U]	330 nF [C1210F334K4RACT U]	330 nF [C1825C334K2RACT U]	330 nF [C2225C334M5UAC TU]
330 nF [C1206C334M3VAC TU]	330 nF [C1210F334K5RACT U]	330 nF [C1825C334K5RACT U]	330 nF [T409A334M025AH 4250]
330 nF [C1206F334K3RACT U]	330 nF [C1812C334K1RACT U]	330 nF [C1825C334M5UAC TU]	330 nF [T491A334M025AT]
330 nF [C1206F334K4RACT U]	330 nF [C1812C334K5RACT U]	330 nF [C2220C334K1GACT U]	330 nF [T491A334M035AT]
330 nF [C1210C334K1RACT U]	330 nF [C1812C334KARACT U]	330 nF [C2220C334K1RACT U]	330 nF [T491B334M050AT]
			330 nF [T494A334M025AT]

Multisim 14.0 Base Components

330 nF [T494A334M035AT]	330 pF [C0603C331K1RACT U]	330 pF [C0805C331K2RACT U]	330 pF [C1206C331KCGAC TU]
330 nF [T494B334M050AT]	330 pF [C0603C331K2RACT U]	330 pF [C0805C331K3GACT U]	330 pF [C1210C331K1GACT U]
330 nF [T496B334M050AT 6110]	330 pF [C0603C331K3GACT U]	330 pF [C0805C331K3RACT U]	330 pF [C1210C331K5GACT U]
330 pF [C0402C331K1HACT U]	330 pF [C0603C331K3RACT U]	330 pF [C0805C331K4RACT U]	330 pF [C1210C331KBGAC TU]
330 pF [C0402C331K3HACT U]	330 pF [C0603C331K4RACT U]	330 pF [C0805C331K5GACT U]	330 pF [C1812C331KBGAC TU]
330 pF [C0402C331K3RACT U]	330 pF [C0603C331K5GACT U]	330 pF [C0805C331K5RACT U]	330 pF [C1825C331KBGAC TU]
330 pF [C0402C331K4GACT U]	330 pF [C0603C331K5RACT U]	330 pF [C0805C331K8RACT U]	330 pF [C2220C331KBGAC TU]
330 pF [C0402C331K4RACT U]	330 pF [C0603C331K8RACT U]	330 pF [C1206C331K1GACT U]	330 pF [C2225C331KBGAC TU]
330 pF [C0402C331K5GACT U]	330 pF [C0805C331K1GACT U]	330 pF [C1206C331K2GACT U]	330 pF [CA064C331K5GAC TU]
330 pF [C0402C331K5HACT U]	330 pF [C0805C331K1RACT U]	330 pF [C1206C331K5GACT U]	330 pF [CA064C331K5RACT U]
330 pF [C0402C331K5RACT U]	330 pF [C0805C331K2GACT U]	330 pF [C1206C331KBGAC TU]	330 uF [A700D337M002AT E007]
330 pF [C0402C331K8RACT U]			

330 uF [A700X337M002AT E010]	330 uF [T491E337M010AT]	330 uF [T495D337M006AT E040]	330 uF [T495X337M010AT E035]
330 uF [A700X337M002AT E015]	330 uF [T491V337M004AT]	330 uF [T495D337M006AT E050]	330 uF [T495X337M010AT E050]
330 uF [A700X337M004AT E010]	330 uF [T491X337M010AT]	330 uF [T495D337M006AT E070]	330 uF [T495X337M010AT E060]
330 uF [A700X337M004AT E015]	330 uF [T494C337M004AT]	330 uF [T495D337M006AT E100]	330 uF [T495X337M010AT E100]
330 uF [A700X337M2R5AT E010]	330 uF [T494D337M004AT]	330 uF [T495D337M010AT E100]	330 uF [T510X337M010AT E035]
330 uF [A700X337M2R5AT E015]	330 uF [T494D337M006AT]	330 uF [T495D337M010AT E125]	330 uF [T513X337M010AH 6110]
330 uF [T489X337M010AT E100]	330 uF [T494D337M010AT]	330 uF [T495D337M010AT E150]	330 uF [T520B337M2R5AT E045]
330 uF [T491C337M004AT]	330 uF [T494E337M006AT]	330 uF [T495E337M010AT E060]	330 uF [T520B337M2R5AT E070]
330 uF [T491D337M004AT]	330 uF [T494E337M010AT]	330 uF [T495X337M006AT E045]	330 uF [T520C337M004AT E025]
330 uF [T491D337M006AT]	330 uF [T494V337M004AT]	330 uF [T495X337M006AT E065]	330 uF [T520C337M2R5AT E015]
330 uF [T491D337M010AT]	330 uF [T494X337M006AT]	330 uF [T495X337M006AT E100]	330 uF [T520C337M2R5AT E025]
330 uF [T491E337M006AT]	330 uF [T494X337M010AT]		
	330 uF [T495D337M004AT E030]		

Multisim 14.0 Base Components

330 uF [T520C337M2R5AT E045]	330 uF [T520D337M006AT E025]	330 uF [T520V337M003AT E025]	330 uF [T520V337M2R5AT E007]
330 uF [T520D337M004AT E006]	330 uF [T520D337M006AT E040]	330 uF [T520V337M004AT E007]	330 uF [T520V337M2R5AT E009]
330 uF [T520D337M004AT E007]	330 uF [T520D337M006AT E045]	330 uF [T520V337M004AT E009]	330 uF [T520V337M2R5AT E012]
330 uF [T520D337M004AT E009]	330 uF [T520D337M2R5AT E006]	330 uF [T520V337M004AT E012]	330 uF [T520V337M2R5AT E015]
330 uF [T520D337M004AT E012]	330 uF [T520D337M2R5AT E007]	330 uF [T520V337M004AT E018]	330 uF [T520V337M2R5AT E018]
330 uF [T520D337M004AT E015]	330 uF [T520L337M2R5AT E009]	330 uF [T520V337M004AT E025]	330 uF [T520V337M2R5AT E025]
330 uF [T520D337M004AT E040]	330 uF [T520L337M2R5AT E012]	330 uF [T520V337M004AT E040]	330 uF [T520V337M2R5AT E040]
330 uF [T520D337M004AT E045]	330 uF [T520L337M2R5AT E025]	330 uF [T520V337M006AT E015]	330 uF [T520W337M2R5A TE025]
330 uF [T520D337M006AT E009]	330 uF [T520V337M003AT E009]	330 uF [T520V337M006AT E025]	330 uF [T520W337M2R5A TE040]
330 uF [T520D337M006AT E010]	330 uF [T520V337M003AT E012]	330 uF [T520V337M006AT E040]	330 uF [T520X337M010AT E010]
330 uF [T520D337M006AT E015]	330 uF [T520V337M003AT E015]	330 uF [T520V337M2R5AT E006]	330 uF [T520X337M010AT E025]

Multisim 14.0 Base Components

330 uF [T520X337M010AT E040]	330 uF [T525D337M2R5AT E025]	330 uF [T530X337M010AT E004]	3554SM 36 mF [C0805C369KBGAC TU]
330 uF [T520Y337M006AT E015]	330 uF [T528Z337M004AT E009]	330 uF [T530X337M010AT E005]	36 pF [C0805C360KBGAC TU]
330 uF [T520Y337M006AT E025]	330 uF [T528Z337M004AT E012]	330 uF [T530X337M010AT E006]	36 pF [C1206C360KBGAC TU]
330 uF [T520Y337M006AT E040]	330 uF [T528Z337M2R5AT E005]	330 uF [T530X337M010AT E010]	36 pF [C1210C360KBGAC TU]
330 uF [T520Y337M010AT E015]	330 uF [T528Z337M2R5AT E007]	330 uF [T530Y337M006AT E006]	36 pF [C1812C360KBGAC TU]
330 uF [T520Y337M010AT E035]	330 uF [T528Z337M2R5AT E008]	330 uF [T541X337M010AH 6520]	36 pF [C1825C360KBGAC TU]
330 uF [T522V337M006AT E040]	330 uF [T528Z337M2R5AT E009]	330 uF [T541Y337M006AH 6510]	36 pF [C2220C360KBGAC TU]
330 uF [T525D337M003AT E025]	330 uF [T528Z337M2R5AT E012]	330 uF [T543C337M2R5AT E045]	36 pF [C2220C360KZGACT U]
330 uF [T525D337M004AT E025]	330 uF [T530D337M004AT E006]	330 uF [T543L337M2R5AT E025]	36 pF [C2225C360KBGAC TU]
330 uF [T525D337M006AT E025]	330 uF [T530D337M006AT E006]	330 uF [T543Y337M006AT E015]	360 pF [C0402C361K1HACT U]
330 uF [T525D337M006AT E040]	330 uF [T530D337M006AT E010]	3-534206-0 3554AM 3554BM	360 pF [C0402C361K3HACT U]

Multisim 14.0 Base Components

360 pF [C0402C361K5HACT U]	39 nF [C0402C393K8RACT U]	39 nF [C0805C393K8RACT U]	39 nF [C1210C393K2RACT U]
360 pF [C0603C361K5GACT U]	39 nF [C0402C393K9RACT U]	39 nF [C0805F393K1RACT U]	39 nF [C1210C393K5RACT U]
360 pF [C1206C361KBGAC TU]	39 nF [C0603C393K1RACT U]	39 nF [C0805F393K3RACT U]	39 nF [C1210C393KARACT U]
360 pF [C1210C361KBGAC TU]	39 nF [C0603C393K3RACT U]	39 nF [C0805F393K4RACT U]	39 nF [C1812C393K1RACT U]
360 pF [C1812C361KBGAC TU]	39 nF [C0603C393K4RACT U]	39 nF [C0805F393K5RACT U]	39 nF [C1812C393K5RACT U]
360 pF [C1825C361KBGAC TU]	39 nF [C0603C393K5RACT U]	39 nF [C1206C393K1RACT U]	39 nF [C2220C393K2GACT U]
360 pF [C2220C361KBGAC TU]	39 nF [C0603C393K8RACT U]	39 nF [C1206C393K4RACT U]	39 pF [C0201C390K3GACT U]
360 pF [C2225C361KBGAC TU]	39 nF [C0805C393K1RACT U]	39 nF [C1206C393K5RACT U]	39 pF [C0402C390K4GACT U]
3-644456-5 3-644456-8	39 nF [C0805C393K3RACT U]	39 nF [C1206C393KARACT U]	39 pF [C0402C390K5GACT U]
39 mF [C0805C399KBGAC TU]	39 nF [C0805C393K4RACT U]	39 nF [C1206C393M1UAC TU]	39 pF [C0402C390K8GACT U]
39 nF [C0402C393K4RACT U]	39 nF [C0805C393K5RACT U]	39 nF [C1210C393K1RACT U]	39 pF [C0603C390K2GACT U]

Multisim 14.0 Base Components

39 pF [C0603C390K5GACT U]	39 pF [C1812C390KBGAC TU]	390 nF [C0805C394K4RACT U]	390 nF [C1210C394K5RACT U]
39 pF [C0805C390K1GACT U]	39 pF [C1825C390KBGAC TU]	390 nF [C0805C394K8RACT U]	390 nF [C1210F394K3RACT U]
39 pF [C0805C390K2GACT U]	39 pF [C2220C390KBGAC TU]	390 nF [C0805C394K9RACT U]	390 nF [C1210F394K4RACT U]
39 pF [C0805C390K5GACT U]	39 pF [C2225C390KBGAC TU]	390 nF [C1206C394K1RACT U]	390 nF [C1210F394K5RACT U]
39 pF [C0805C390KBGAC TU]	39 pF [CA064C390K5GAC TU]	390 nF [C1206C394K3RACT U]	390 nF [C1812C394K1RACT U]
39 pF [C0805C390KCGAC TU]	390 nF [C0603C394K4PACT U]	390 nF [C1206C394K4RACT U]	390 nF [C1812C394K5RACT U]
39 pF [C1206C390K1GACT U]	390 nF [C0603C394K4RACT U]	390 nF [C1206C394K5RACT U]	390 nF [C1812C394KARACT U]
39 pF [C1206C390K2GACT U]	390 nF [C0603C394K8PACT U]	390 nF [C1206C394K8RACT U]	390 nF [C1812C394M5UAC TU]
39 pF [C1206C390K5GACT U]	390 nF [C0603C394K8RACT U]	390 nF [C1206F394K3RACT U]	390 nF [C1812F394K1RACT U]
39 pF [C1206C390KBGAC TU]	390 nF [C0603C394K9RACT U]	390 nF [C1206F394K4RACT U]	390 nF [C1812F394K2RACT U]
39 pF [C1210C390KBGAC TU]	390 nF [C0805C394K3RACT U]	390 nF [C1210C394K3RACT U]	390 nF [C1812F394K3RACT U]

Multisim 14.0 Base Components

390 nF [C1812F394K5RACT U]	390 pF [C0402C391K5RACT U]	390 pF [C0805C391K4RACT U]	390 pF [C2220C391KBGAC TU]
390 nF [C1825C394K1RACT U]	390 pF [C0603C391K1RACT U]	390 pF [C0805C391K5GACT U]	390 pF [C2225C391KBGAC TU]
390 nF [C1825C394K2RACT U]	390 pF [C0603C391K2RACT U]	390 pF [C0805C391K5RACT U]	390 pF [CA064C391K5GAC TU]
390 nF [C1825C394K5RACT U]	390 pF [C0603C391K3GACT U]	390 pF [C1206C391K1GACT U]	390 uF [A700X397M002AT E010]
390 nF [C2225C394K1RACT U]	390 pF [C0603C391K3RACT U]	390 pF [C1206C391K2GACT U]	390 uF [A700X397M002AT E015]
390 nF [C2225C394K2RACT U]	390 pF [C0603C391K4RACT U]	390 pF [C1206C391K5GACT U]	3BH41
390 pF [C0402C391K1HACT U]	390 pF [C0603C391K5GACT U]	390 pF [C1206C391KBGAC TU]	3GH41
390 pF [C0402C391K3HACT U]	390 pF [C0603C391K5RACT U]	390 pF [C1206C391KCGAC TU]	3JH41
390 pF [C0402C391K3RACT U]	390 pF [C0805C391K1GACT U]	390 pF [C1210C391KBGAC TU]	3KASMC15AHE3/57 T
390 pF [C0402C391K4RACT U]	390 pF [C0805C391K1RACT U]	390 pF [C1812C391KBGAC TU]	3KASMC24AHE3/9A T
390 pF [C0402C391K5HACT U]	390 pF [C0805C391K2GACT U]	390 pF [C1825C391KBGAC TU]	3KASMC28AHM3/5 7T
			3Line_Bussed
			3Line_Isolated
			3LN01M-TL-E
			3LN01M-TL-H
			3LN01SS-TL-E
			3LN01SS-TL-H

Multisim 14.0 Base Components

3LP01SS-TL-E	4.3 nF [C0603C432K3HACT U]	4.7 nF [C0402C472K5RACT U]	4.7 nF [C0603C472K8RACT U]
3LP01SS-TL-H			
3LP01S-TL-E	4.3 nF [C0603C432K5HACT U]	4.7 nF [C0402C472K8RACT U]	4.7 nF [C0603C472K9RACT U]
3N246			
3N247	4.3 nF	4.7 nF	4.7 nF
3N248	[C0805C432K1GACT U]	[C0402C472K9RACT U]	[C0805C472K1GACT U]
3N249			
3N250	4.3 nF [C0805C432K1HACT U]	4.7 nF [C0603C472K1HACT U]	4.7 nF [C0805C472K1HACT U]
3N251			
3N252	4.3 nF [C0805C432K3HACT U]	4.7 nF [C0603C472K1RACT U]	4.7 nF [C0805C472K1RACT U]
3N253			
3N254	4.3 nF [C0805C432K5HACT U]	4.7 nF [C0603C472K3GACT U]	4.7 nF [C0805C472K2RACT U]
3N255			
3N256	4.3 nF	4.7 nF	4.7 nF
3N257	[C1825C432KBGAC TU]	[C0603C472K3HACT U]	[C0805C472K3GACT U]
3N258			
3N259	4.3 nF [C2220C432KBGAC TU]	4.7 nF [C0603C472K3RACT U]	4.7 nF [C0805C472K3HACT U]
3PDT_DB			
3PDT_SB	4.3 nF [C2225C432KBGAC TU]	4.7 nF [C0603C472K4RACT U]	4.7 nF [C0805C472K3RACT U]
3PST_DB			
3PST_SB	4.7 nF [C0402C472K3RACT U]	4.7 nF [C0603C472K5HACT U]	4.7 nF [C0805C472K4RACT U]
4.3 nF [C0603C432K1HACT U]	4.7 nF [C0402C472K4RACT U]	4.7 nF [C0603C472K5RACT U]	4.7 nF [C0805C472K5HACT U]

Multisim 14.0 Base Components

4.7 nF [C0805C472K5RACT U]	4.7 nF [C1210C472K5GACT U]	4.7 nF [CA064C472K5RACT U]	4.7 uF [C1206C475K5PACT U]
4.7 nF [C0805C472KARACT U]	4.7 nF [C1210C472K5RACT U]	4.7 uF [C0603C475K8PACT U]	4.7 uF [C1206C475K8NAC TU]
4.7 nF [C1206C472K1RACT U]	4.7 nF [C1812C472K1GACT U]	4.7 uF [C0603C475K9PACT U]	4.7 uF [C1206C475K8PACT U]
4.7 nF [C1206C472K2RACT U]	4.7 nF [C1812C472K2GACT U]	4.7 uF [C0805C475K3PACT U]	4.7 uF [C1206C475K8RACT U]
4.7 nF [C1206C472K3RACT U]	4.7 nF [C1812C472K5GACT U]	4.7 uF [C0805C475K4PACT U]	4.7 uF [C1206C475K9PACT U]
4.7 nF [C1206C472K4GACT U]	4.7 nF [C1825C472K2GACT U]	4.7 uF [C0805C475K8PACT U]	4.7 uF [C1206C475K9RACT U]
4.7 nF [C1206C472K5GACT U]	4.7 nF [C1825C472K5GACT TU]	4.7 uF [C0805C475K9PACT U]	4.7 uF [C1210C475K3NAC TU]
4.7 nF [C1206C472K5RACT U]	4.7 nF [C2220C472K5GACT TU]	4.7 uF [C1206C475K3PACT U]	4.7 uF [C1210C475K3PACT U]
4.7 nF [C1210C472K1GACT U]	4.7 nF [C2225C472K2GACT U]	4.7 uF [C1206C475K3RACT U]	4.7 uF [C1210C475K3RACT U]
4.7 nF [C1210C472K1RACT U]	4.7 nF [C2225C472K5GACT TU]	4.7 uF [C1206C475K4PACT U]	4.7 uF [C1210C475K4PACT U]
4.7 nF [C1210C472K2RACT U]	4.7 nF [CA064C472K3RACT U]	4.7 uF [C1206C475K4RACT U]	4.7 uF [C1210C475K4RACT U]

Multisim 14.0 Base Components

4.7 uF [C1210C475K5R1C7 186]	4.7 uF [T491A475M010AT]	4.7 uF [T491T475M016AT]	4.7 uF [T494D475M050AT]
4.7 uF [C1210C475K5RACT U]	4.7 uF [T491A475M016AT]	4.7 uF [T494A475M004AT]	4.7 uF [T494S475M006AT]
4.7 uF [C1210C475K8PACT U]	4.7 uF [T491A475M020AT]	4.7 uF [T494A475M006AT]	4.7 uF [T494S475M010AT]
4.7 uF [C1210C475K8RACT U]	4.7 uF [T491B475M010AT]	4.7 uF [T494A475M010AT]	4.7 uF [T494T475M016AT]
4.7 uF [C1210C475K8RACT U]	4.7 uF [T491B475M016AT]	4.7 uF [T494A475M016AT]	4.7 uF [T495A475M010AT E1K3]
4.7 uF [C1210C475K9PACT U]	4.7 uF [T491B475M020AT]	4.7 uF [T494A475M020AT]	4.7 uF [T495B475M016AT E700]
4.7 uF [C1210C475K9RACT U]	4.7 uF [T491B475M025AT]	4.7 uF [T494B475M010AT]	4.7 uF [T495C475M035AT E450]
4.7 uF [C1210C475M4VAC TU]	4.7 uF [T491C475M020AT]	4.7 uF [T494B475M016AT]	4.7 uF [T495C475M035AT E500]
4.7 uF [C1210C475M8VAC TU]	4.7 uF [T491C475M025AT]	4.7 uF [T494B475M020AT]	4.7 uF [T495C475M035AT E600]
4.7 uF [T409D475M010AH 4250]	4.7 uF [T491C475M035AT]	4.7 uF [T494B475M025AT]	4.7 uF [T495C475M035AT E600]
4.7 uF [T429C475M006AH 4250]	4.7 uF [T491D475M035AT]	4.7 uF [T494C475M010AT]	4.7 uF [T495D475M050AT E275]
4.7 uF [T491A475M004AT]	4.7 uF [T491D475M050AT]	4.7 uF [T494C475M020AT]	4.7 uF [T495D475M050AT E300]
4.7 uF [T491A475M006AT]	4.7 uF [T491S475M006AT]	4.7 uF [T494C475M025AT]	4.7 uF [T495D475M050AT E300]
		4.7 uF [T494D475M035AT]	4.7 uF [T495X475M050AT E300]

Multisim 14.0 Base Components

4.7 uF [T498A475M010AT E2K9]	4001BD_10V	4008BP_5V	4010BC1_10V
	4001BD_15V	4008BP_5V	4010BC1_15V
4.7 uF [T498B475M010AT E2K7]	4001BD_5V	4008BT_10V	4010BC1_5V
	4001BP_10V	4008BT_15V	4010BEY_10V
	4001BP_15V	4008BT_5V	4010BEY_15V
4.7 uF [T498B475M016AT E2K1]	4001BP_5V	4009BCL_10V	4010BEY_5V
	4001BP_5V	4009BCL_15V	4010BF_10V
4.7 uF [T521D475M063AT E075]	4001BT_10V	4009BCL_5V	4010BF_15V
	4001BT_15V	4009BCP_10V	4010BF_5V
4.7 uF [T521D475M063AT E300]	4001BT_5V	4009BCP_15V	4010BF_5V
	4002BD_10V	4009BCP_5V	4010BM1_10V
4.7 uF [T540D475M063AH 6510]	4002BD_15V	4009BCP_5V	4010BM1_15V
	4002BD_5V	4009BD_10V	4010BM1_5V
4 AMP	4002BP_10V	4009BD_15V	4011BD_10V
40 AMP	4002BP_15V	4009BD_5V	4011BD_15V
4000BD_10V	4002BP_5V	40106BD_10V	4011BD_5V
4000BD_15V	4002BP_5V	40106BD_15V	4011BP_10V
4000BD_5V	4002BT_10V	40106BD_5V	4011BP_15V
4000BP_10V	4002BT_15V	40106BP_10V	4011BP_5V
4000BP_15V	4002BT_5V	40106BP_15V	4011BP_5V
4000BP_5V	4008BD_10V	40106BP_5V	4011BT_10V
4000BP_5V	4008BD_15V	40106BP_5V	4011BT_15V
4000BT_10V	4008BD_5V	40106BT_10V	4011BT_5V
4000BT_15V	4008BP_10V	40106BT_15V	4012BD_10V
4000BT_5V	4008BP_15V	40106BT_5V	4012BD_15V

Multisim 14.0 Base Components

4012BD_5V	4014BT_10V	4019BD_15V	4024BP_5V
4012BP_10V	4014BT_15V	4019BD_5V	4024BT_10V
4012BP_15V	4014BT_5V	4019BP_10V	4024BT_15V
4012BP_5V	4015BD_10V	4019BP_15V	4024BT_5V
4012BP_5V	4015BD_15V	4019BP_5V	4025BD_10V
4012BT_10V	4015BD_5V	4019BP_5V	4025BD_15V
4012BT_15V	4015BP_10V	4019BT_10V	4025BD_5V
4012BT_5V	4015BP_15V	4019BT_15V	4025BP_10V
4013BD_10V	4015BP_5V	4019BT_5V	4025BP_15V
4013BD_15V	4015BP_5V	4023BD_10V	4025BP_5V
4013BD_5V	4015BT_10V	4023BD_15V	4025BP_5V
4013BP_10V	4015BT_15V	4023BD_5V	4025BT_10V
4013BP_15V	4015BT_5V	4023BP_10V	4025BT_15V
4013BP_5V	4017BD_10V	4023BP_15V	4025BT_5V
4013BP_5V	4017BD_15V	4023BP_5V	4027BD_10V
4013BT_10V	4017BD_5V	4023BP_5V	4027BD_15V
4013BT_15V	4017BP_10V	4023BT_10V	4027BD_5V
4013BT_5V	4017BP_10V	4023BT_15V	4027BP_10V
4014BD_10V	4017BP_15V	4023BT_5V	4027BP_15V
4014BD_15V	4017BP_5V	4024BD_10V	4027BP_5V
4014BD_5V	4017BP_5V	4024BD_15V	4027BP_5V
4014BP_10V	4017BT_10V	4024BD_5V	4027BT_10V
4014BP_15V	4017BT_15V	4024BP_10V	4027BT_15V
4014BP_5V	4017BT_5V	4024BP_15V	4027BT_5V
4014BP_5V	4019BD_10V	4024BP_5V	4028BD_10V

Multisim 14.0 Base Components

4028BD_15V	4040BP_5V	4043BD_15V	4049BP_5V
4028BD_5V	4040BT_10V	4043BD_5V	4049BT_10V
4028BP_10V	4040BT_15V	4043BP_10V	4049BT_15V
4028BP_15V	4040BT_5V	4043BP_15V	4049BT_5V
4028BP_5V	4041BD_10V	4043BP_5V	4050BD_10V
4028BP_5V	4041BD_15V	4043BP_5V	4050BD_15V
4028BT_10V	4041BD_5V	4043BT_10V	4050BD_5V
4028BT_15V	4041BP_10V	4043BT_15V	4050BP_10V
4028BT_5V	4041BP_15V	4043BT_5V	4050BP_15V
4030BD_10V	4041BP_5V	4044BD_10V	4050BP_5V
4030BD_15V	4041BP_5V	4044BD_15V	4050BP_5V
4030BD_5V	4041BT_10V	4044BD_5V	4050BT_10V
4030BP_10V	4041BT_15V	4044BP_10V	4050BT_15V
4030BP_15V	4041BT_5V	4044BP_15V	4050BT_5V
4030BP_5V	4042BD_10V	4044BP_5V	4066BD_10V
4030BP_5V	4042BD_15V	4044BP_5V	4066BD_15V
4030BT_10V	4042BD_5V	4044BT_10V	4066BD_5V
4030BT_15V	4042BP_10V	4044BT_15V	4066BP_10V
4030BT_5V	4042BP_15V	4044BT_5V	4066BP_15V
4040BD_10V	4042BP_5V	4049BD_10V	4066BP_5V
4040BD_15V	4042BP_5V	4049BD_15V	4066BT_10V
4040BD_5V	4042BT_10V	4049BD_5V	4066BT_15V
4040BP_10V	4042BT_15V	4049BP_10V	4066BT_5V
4040BP_15V	4042BT_5V	4049BP_15V	4068BD_10V
4040BP_5V	4043BD_10V	4049BP_5V	4068BD_15V

Multisim 14.0 Base Components

4068BD_5V	4070BT_10V	4073BD_5V	4076BT_10V
4068BP_10V	4070BT_15V	4073BP_10V	4076BT_15V
4068BP_15V	4070BT_5V	4073BP_15V	4076BT_5V
4068BP_5V	4071BD_10V	4073BP_5V	4077BD_10V
4068BP_5V	4071BD_15V	4073BP_5V	4077BD_15V
4068BT_10V	4071BD_5V	4073BT_10V	4077BD_5V
4068BT_15V	4071BP_10V	4073BT_15V	4077BP_10V
4068BT_5V	4071BP_15V	4073BT_5V	4077BP_15V
4069BCL_10V	4071BP_5V	4075BD_10V	4077BP_5V
4069BCL_15V	4071BP_5V	4075BD_15V	4077BP_5V
4069BCL_5V	4071BT_10V	4075BD_5V	4077BT_10V
4069BCP_10V	4071BT_15V	4075BP_10V	4077BT_15V
4069BCP_15V	4071BT_5V	4075BP_15V	4077BT_5V
4069BCP_5V	4072BD_10V	4075BP_5V	4078BD_10V
4069BCP_5V	4072BD_15V	4075BP_5V	4078BD_15V
4069BD_10V	4072BD_5V	4075BT_10V	4078BD_5V
4069BD_15V	4072BP_10V	4075BT_15V	4078BP_10V
4069BD_5V	4072BP_15V	4075BT_5V	4078BP_15V
4070BD_10V	4072BP_5V	4076BD_10V	4078BP_5V
4070BD_15V	4072BP_5V	4076BD_15V	4078BP_5V
4070BD_5V	4072BT_10V	4076BD_5V	4078BT_10V
4070BP_10V	4072BT_15V	4076BD_5V	4078BT_15V
4070BP_15V	4072BT_5V	4076BP_10V	4078BT_5V
4070BP_5V	4073BD_10V	4076BP_15V	4081BD_10V
4070BP_5V	4073BD_15V	4076BP_5V	4081BD_15V

Multisim 14.0 Base Components

4081BD_5V	4085BT_10V	43 mF [C0805C439KBGAC TU]	430 pF [C0603C431K1HACT U]
4081BP_10V	4085BT_15V		
4081BP_15V	4085BT_5V	43 pF [C0805C430KBGAC TU]	430 pF [C0603C431K3HACT U]
4081BP_5V	4086BD_10V		
4081BP_5V	4086BD_15V	43 pF [C1206C430KBGAC TU]	430 pF [C0603C431K5HACT U]
4081BT_10V	4086BD_5V		
4081BT_15V	4086BD_5V	43 pF [C1210C430KBGAC TU]	430 pF [C1206C431KBGAC TU]
4081BT_5V	4086BP_10V		
4082BD_10V	4086BP_15V	43 pF [C1812C430KBGAC TU]	430 pF [C1210C431KBGAC TU]
4082BD_15V	4086BP_5V		
4082BD_5V	4086BT_10V	43 pF [C1825C430KBGAC TU]	430 pF [C1812C431KBGAC TU]
4082BP_10V	4086BT_15V		
4082BP_15V	4086BT_5V	43 pF [C2220C430KBGAC TU]	430 pF [C1825C431KBGAC TU]
4082BP_5V	4093BD_10V		
4082BP_5V	4093BD_15V	43 pF [C2225C430KBGAC TU]	430 pF [C2220C431KBGAC TU]
4082BT_10V	4093BD_5V		
4082BT_15V	4093BP_10V	430 pF [C0402C431K1HACT U]	430 pF [C2225C431KBGAC TU]
4082BT_5V	4093BP_15V		
4085BD_10V	4093BP_5V	430 pF [C0402C431K3HACT U]	4502BD_10V
4085BD_15V	4093BP_5V		4502BD_15V
4085BD_5V	4093BT_10V	430 pF [C0402C431K5HACT U]	4502BD_5V
4085BP_10V	4093BT_15V		4502BP_10V
4085BP_15V	4093BT_5V		4502BP_15V
4085BP_5V	413990-1		
4085BP_5V			

Multisim 14.0 Base Components

4502BP_5V	4510BD_10V	4512BP_5V	4516BD_10V
4502BP_5V	4510BD_15V	4512BP_5V	4516BD_15V
4502BT_10V	4510BD_5V	4512BT_10V	4516BD_5V
4502BT_15V	4510BP_10V	4512BT_15V	4516BP_10V
4502BT_5V	4510BP_15V	4512BT_5V	4516BP_15V
4503BCL_10V	4510BP_5V	4514BD_10V	4516BP_5V
4503BCL_15V	4510BP_5V	4514BD_15V	4516BP_5V
4503BCL_5V	4510BT_10V	4514BD_5V	4516BT_10V
4503BCP_10V	4510BT_15V	4514BP_10V	4516BT_15V
4503BCP_15V	4510BT_5V	4514BP_15V	4516BT_5V
4503BCP_5V	4511BD_10V	4514BP_5V	4518BD_10V
4503BCP_5V	4511BD_15V	4514BP_5V	4518BD_15V
4503BD_10V	4511BD_5V	4514BT_10V	4518BD_5V
4503BD_15V	4511BP_10V	4514BT_15V	4518BP_10V
4503BD_5V	4511BP_15V	4514BT_5V	4518BP_15V
4508BD_10V	4511BP_5V	4515BD_10V	4518BP_5V
4508BD_15V	4511BP_5V	4515BD_15V	4518BP_5V
4508BD_5V	4511BT_10V	4515BD_5V	4518BT_10V
4508BP_10V	4511BT_15V	4515BP_10V	4518BT_15V
4508BP_15V	4511BT_5V	4515BP_15V	4518BT_5V
4508BP_5V	4512BD_10V	4515BP_5V	4520BD_10V
4508BP_5V	4512BD_15V	4515BP_5V	4520BD_15V
4508BT_10V	4512BD_5V	4515BT_10V	4520BD_5V
4508BT_15V	4512BP_10V	4515BT_15V	4520BP_10V
4508BT_5V	4512BP_15V	4515BT_5V	4520BP_15V

Multisim 14.0 Base Components

4520BP_5V	4585BD_15V	47 nF [C0402C473K8RACT U]	47 nF [C0805C473K1RACT U]
4520BP_5V	4585BD_5V		
4520BT_10V	4585BP_15V	47 nF [C0402C473K9PACT U]	47 nF [C0805C473K3RACT U]
4520BT_15V	4585BP_5V		
4520BT_5V	4585BT_15V	47 nF [C0402C473K9RACT U]	47 nF [C0805C473K4RACT U]
4532BD_10V	4585BT_5V		
4532BD_15V	45970-4185		
4532BD_5V	4-644456-0	47 nF [C0603C473K1RACT U]	47 nF [C0805C473K5RACT U]
4532BP_10V	46765-1001		
4532BP_15V	46765-2001	47 nF [C0603C473K3NAC TU]	47 nF [C0805C473K8RACT U]
4532BP_5V	47 mF [C0805C479KBGAC TU]		
4532BP_5V		47 nF [C0603C473K3RACT U]	47 nF [C0805C473M5UAC TU]
4532BT_10V	47 mF [C1206C479K1GACT U]		
4532BT_15V		47 nF [C0603C473K4RACT U]	47 nF [C0805C473M5VAC TU]
4532BT_5V	47 nF [C0402C473K3RACT U]		
4556BD_10V		47 nF [C0603C473K5NAC TU]	47 nF [C0805F473K3RACT U]
4556BD_15V	47 nF [C0402C473K4PACT U]		
4556BD_5V		47 nF [C0603C473K5RACT U]	47 nF [C0805F473K4RACT U]
4556BP_10V			
4556BP_15V	47 nF [C0402C473K4RACT U]		
4556BP_5V		47 nF [C0603C473K8RACT U]	47 nF [C0805F473K5RACT U]
4556BP_5V	47 nF [C0402C473K8PACT U]		
4556BT_10V		47 nF [C0603C473M3VAC TU]	47 nF [C1206C473K1HACT U]
4556BT_15V			
4556BT_5V			

Multisim 14.0 Base Components

47 nF [C1206C473K1RACT U]	47 nF [C1206F473K4RACT U]	47 nF [C1210C473KARACT U]	47 nF [C2220C473K5GACT U]
47 nF [C1206C473K3GACT U]	47 nF [C1206F473K5RACT U]	47 nF [C1812C473K1GACT U]	47 nF [CA064C473K4RACT U]
47 nF [C1206C473K3HACT U]	47 nF [C1210C473K1GACT U]	47 nF [C1812C473K1HACT U]	47 nF [CA064C473K8RACT U]
47 nF [C1206C473K3RACT U]	47 nF [C1210C473K1HACT U]	47 nF [C1812C473K1RACT U]	47 pF [C0201C470K3GACT U]
47 nF [C1206C473K4RACT U]	47 nF [C1210C473K1RACT U]	47 nF [C1812C473K2RACT U]	47 pF [C0402C470K3GACT U]
47 nF [C1206C473K5HACT U]	47 nF [C1210C473K2RACT U]	47 nF [C1812C473K5GACT U]	47 pF [C0402C470K4GACT U]
47 nF [C1206C473K5RACT U]	47 nF [C1210C473K3GACT U]	47 nF [C1812C473K5HACT U]	47 pF [C0402C470K5GACT U]
47 nF [C1206C473KARACT U]	47 nF [C1210C473K3HACT U]	47 nF [C1812C473K5RACT U]	47 pF [C0402C470K8GACT U]
47 nF [C1206C473M5UAC TU]	47 nF [C1210C473K5GACT U]	47 nF [C1825C473K5RACT U]	47 pF [C0603C470K1GACT U]
47 nF [C1206F473K1RACT U]	47 nF [C1210C473K5HACT U]	47 nF [C2220C473K1GACT U]	47 pF [C0603C470K5GACT U]
47 nF [C1206F473K3RACT U]	47 nF [C1210C473K5RACT U]	47 nF [C2220C473K2GACT U]	47 pF [C0603C470K8GACT U]

Multisim 14.0 Base Components

47 pF [C0805C470K1GACT U]	47 pF [C1206C470KDGAC TU]	47 pF [CA064C470K5GAC TU]	47 uF [T491C476M006AT]
47 pF [C0805C470K2GACT U]	47 pF [C1206C470KFGACT U]	47 pF [CA064C470K8GAC TU]	47 uF [T491C476M010AT]
47 pF [C0805C470K3GACT U]	47 pF [C1206C470KGGAC TU]	47 uF [A700V476M006AT E018]	47 uF [T491C476M020AT]
47 pF [C0805C470K5GACT U]	47 pF [C1210C470K5GACT U]	47 uF [A700V476M006AT E025]	47 uF [T491D476M006AT]
47 pF [C0805C470KBGAC TU]	47 pF [C1210C470KBGAC TU]	47 uF [A700V476M006AT E028]	47 uF [T491D476M010AT]
47 pF [C0805C470KCGAC TU]	47 pF [C1812C470KBGAC TU]	47 uF [T409H476M010AH 4250]	47 uF [T491D476M016AT]
47 pF [C1206C470K1GACT U]	47 pF [C1812C470KDGAC TU]	47 uF [T419F476M010AH 4250]	47 uF [T491D476M020AT]
47 pF [C1206C470K2GACT U]	47 pF [C1825C470KBGAC TU]	47 uF [T491A476M004AT]	47 uF [T491D476M025AT]
47 pF [C1206C470K3GACT U]	47 pF [C2220C470KBGAC TU]	47 uF [T491A476M006AT]	47 uF [T491E476M035AT]
47 pF [C1206C470K5GACT U]	47 pF [C2225C470KBGAC TU]	47 uF [T491B476M004AT]	47 uF [T491T476M004AT]
47 pF [C1206C470KBGAC TU]	47 pF [CA064C470K3GAC TU]	47 uF [T491B476M006AT]	47 uF [T491T476M006AT]
		47 uF [T491B476M010AT]	47 uF [T491U476M004AT]
		47 uF [T491C476M004AT]	

Multisim 14.0 Base Components

47 uF [T491U476M006AT]	47 uF [T494C476M020AT]	47 uF [T494V476M010AT]	47 uF [T495D476M016AT E150]
47 uF [T491U476M010AT]	47 uF [T494D476M006AT]	47 uF [T494V476M016AT]	47 uF [T495D476M020AT E100]
47 uF [T491V476M010AT]	47 uF [T494D476M010AT]	47 uF [T494X476M025AT]	47 uF [T495D476M020AT E175]
47 uF [T491V476M016AT]	47 uF [T494D476M016AT]	47 uF [T495B476M006AT E450]	47 uF [T495D476M025AT E120]
47 uF [T491X476M025AT]	47 uF [T494D476M020AT]	47 uF [T495B476M010AT E500]	47 uF [T495D476M025AT E250]
47 uF [T491X476M035AT]	47 uF [T494D476M025AT]	47 uF [T495C476M016AT E350]	47 uF [T495V476M006AT E150]
47 uF [T494A476M004AT]	47 uF [T494E476M035AT]	47 uF [T495D476M010AT E080]	47 uF [T495X476M020AT E065]
47 uF [T494A476M006AT]	47 uF [T494T476M004AT]	47 uF [T495D476M010AT E090]	47 uF [T495X476M020AT E100]
47 uF [T494B476M004AT]	47 uF [T494T476M006AT]	47 uF [T495D476M010AT E200]	47 uF [T495X476M020AT E150]
47 uF [T494B476M010AT]	47 uF [T494U476M004AT]	47 uF [T495D476M016AT E080]	47 uF [T495X476M025AT E080]
47 uF [T494C476M004AT]	47 uF [T494U476M006AT]	47 uF [T495D476M016AT E100]	47 uF [T495X476M025AT E150]
47 uF [T494C476M006AT]	47 uF [T494U476M010AT]		
47 uF [T494C476M010AT]			
47 uF [T494C476M016AT]			

Multisim 14.0 Base Components

47 uF [T495X476M025AT E185]	47 uF [T510X476M035AT E065]	47 uF [T520B476M010AT E035]	47 uF [T520W476M016AT E045]
47 uF [T495X476M025AT E200]	47 uF [T520A476M004AT E070]	47 uF [T520B476M010AT E070]	47 uF [T521D476M020AT E055]
47 uF [T495X476M035AT E185]	47 uF [T520A476M004AT E080]	47 uF [T520C476M010AT E100]	47 uF [T521V476M020AT E090]
47 uF [T495X476M035AT E200]	47 uF [T520A476M006AT E150]	47 uF [T520D476M016AT E035]	47 uF [T521W476M020AT E045]
47 uF [T495X476M035AT E300]	47 uF [T520A476M2R5AT E090]	47 uF [T520D476M016AT E070]	47 uF [T521X476M035AT E030]
47 uF [T497G476M006AT 6110]	47 uF [T520B476M006AT E025]	47 uF [T520Q476M011AT E040]	47 uF [T521X476M035AT E070]
47 uF [T498C476M006AT E800]	47 uF [T520B476M006AT E035]	47 uF [T520T476M004AT E070]	47 uF [T525B476M006AT E080]
47 uF [T498D476M010AT E600]	47 uF [T520B476M006AT E040]	47 uF [T520T476M006AT E040]	47 uF [T525D476M016AT E035]
47 uF [T498D476M016AT E600]	47 uF [T520B476M006AT E070]	47 uF [T520T476M006AT E070]	47 uF [T525D476M016AT E065]
47 uF [T510E476M035AT E050]	47 uF [T520B476M008AT E035]	47 uF [T520V476M016AT E045]	47 uF [T525T476M006AT E080]
47 uF [T510X476M035AT E055]	47 uF [T520B476M008AT E070]	47 uF [T520V476M016AT E070]	47 uF [T543A476M004AT E080]

Multisim 14.0 Base Components

47 uF [T543W476M016AT E045]	470 nF [C0805C474K4RACT U]	470 nF [C1206C474M4VAC TU]	470 nF [C1812C474K5RACT U]
470 nF [C0402C474K9PACT U]	470 nF [C0805C474K8RACT U]	470 nF [C1206F474K3RACT U]	470 nF [C1812C474KARACT U]
470 nF [C0603C474K4PACT U]	470 nF [C0805C474M3VAC TU]	470 nF [C1206F474K4RACT U]	470 nF [C1812C474M5UAC TU]
470 nF [C0603C474K4RACT U]	470 nF [C0805C474M4VAC TU]	470 nF [C1210C474K3RACT U]	470 nF [C1812F474K1RACT U]
470 nF [C0603C474K8PACT U]	470 nF [C1206C474K3NAC TU]	470 nF [C1210C474K4RACT U]	470 nF [C1812F474K3RACT U]
470 nF [C0603C474K8RACT U]	470 nF [C1206C474K3RACT U]	470 nF [C1210C474K5RACT U]	470 nF [C1812F474K5RACT U]
470 nF [C0603C474K9PACT U]	470 nF [C1206C474K4RACT U]	470 nF [C1210C474M5UAC TU]	470 nF [C1825C474K1RACT U]
470 nF [C0603C474K9RACT U]	470 nF [C1206C474K5NAC TU]	470 nF [C1210F474K1RACT U]	470 nF [C1825C474K5RACT U]
470 nF [C0805C474K3NAC TU]	470 nF [C1206C474K5RACT U]	470 nF [C1210F474K3RACT U]	470 nF [C1825C474KARACT U]
470 nF [C0805C474K3PACT U]	470 nF [C1206C474K8RACT U]	470 nF [C1210F474K4RACT U]	470 nF [C2220C474K1RACT U]
470 nF [C0805C474K3RACT U]	470 nF [C1206C474M3VAC TU]	470 nF [C1210F474K5RACT U]	470 nF [C2220C474K5RACT U]

Multisim 14.0 Base Components

470 nF [C2220C474KARACT U]	470 nF [T494A474M035AT]	470 pF [C0402C471K8RACT U]	470 pF [C0603C471K5RACT U]
470 nF [C2225C474K1RACT U]	470 nF [T494B474M035AT]	470 pF [C0402C471K9RACT U]	470 pF [C0603C471K8RACT U]
470 nF [C2225C474K2RACT U]	470 nF [T494C474M050AT]	470 pF [C0603C471K1HACT U]	470 pF [C0805C471K1GACT U]
470 nF [C2225C474K5RACT U]	470 nF [T498A474M025AT E8K5]	470 pF [C0603C471K1RACT U]	470 pF [C0805C471K1RACT U]
470 nF [C2225C474KARACT U]	470 pF [C0402C471K1HACT U]	470 pF [C0603C471K2RACT U]	470 pF [C0805C471K2GACT U]
470 nF [C2225C474M1UAC TU]	470 pF [C0402C471K3GACT U]	470 pF [C0603C471K3GACT U]	470 pF [C0805C471K2RACT U]
470 nF [CDR06BX474AKSM]	470 pF [C0402C471K3HACT U]	470 pF [C0603C471K3HACT U]	470 pF [C0805C471K3RACT U]
470 nF [T491A474M025AT]	470 pF [C0402C471K3RACT U]	470 pF [C0603C471K3RACT U]	470 pF [C0805C471K4RACT U]
470 nF [T491A474M035AT]	470 pF [C0402C471K4RACT U]	470 pF [C0603C471K4RACT U]	470 pF [C0805C471K5GACT U]
470 nF [T491B474M035AT]	470 pF [C0402C471K5HACT U]	470 pF [C0603C471K5GACT U]	470 pF [C0805C471K5RACT U]
470 nF [T491C474M050AT]	470 pF [C0402C471K5RACT U]	470 pF [C0603C471K5HACT U]	470 pF [C0805C471KARACT U]
470 nF [T494A474M025AT]			

Multisim 14.0 Base Components

470 pF [C1206C471K1GACT U]	470 pF [C2220C471KBGAC TU]	470 uF [T491D477M006AT]	470 uF [T495D477M006AT E100]
470 pF [C1206C471K2GACT U]	470 pF [C2225C471KBGAC TU]	470 uF [T491E477M006AT]	470 uF [T495D477M006AT E125]
470 pF [C1206C471K5GACT U]	470 pF [CA064C471K4RACT U]	470 uF [T491E477M010AT]	470 uF [T495E477M006AT E040]
470 pF [C1206C471KBGAC TU]	470 pF [CA064C471K5GAC TU]	470 uF [T491X477M006AT]	470 uF [T495X477M004AT E030]
470 pF [C1206C471KCGAC TU]	470 pF [CA064C471K5RACT U]	470 uF [T491X477M010AT]	470 uF [T495X477M004AT E045]
470 pF [C1210C471K5GACT U]	470 pF [CA064C471K8RAC]	470 uF [T494D477M004AT]	470 uF [T495X477M004AT E100]
470 pF [C1210C471KBGAC TU]	470 uF [A700X477M002AT E007]	470 uF [T494D477M006AT]	470 uF [T495X477M006AT E030]
470 pF [C1210C471KCGAC TU]	470 uF [A700X477M002AT E010]	470 uF [T494E477M006AT]	470 uF [T495X477M006AT E045]
470 pF [C1812C471K5GACT U]	470 uF [A700X477M002AT E015]	470 uF [T494X477M004AT]	470 uF [T495X477M006AT E050]
470 pF [C1812C471KBGAC TU]	470 uF [T489X477M006AT E200]	470 uF [T494X477M006AT]	470 uF [T495X477M006AT E065]
470 pF [C1825C471KBGAC TU]	470 uF [T491D477M004AT]	470 uF [T494X477M010AT]	470 uF [T495X477M010AT E045]
		470 uF [T495D477M006AT E045]	

Multisim 14.0 Base Components

470 uF [T495X477M010AT E050]	470 uF [T520D477M004AT E018]	470 uF [T520V477M2R5AT E012]	470 uF [T520Y477M006AT E025]
470 uF [T495X477M010AT E060]	470 uF [T520D477M004AT E025]	470 uF [T520V477M2R5AT E015]	470 uF [T522Y477M006AT E040]
470 uF [T495X477M010AT E100]	470 uF [T520D477M004AT E040]	470 uF [T520V477M2R5AT E018]	470 uF [T525D477M003AT E025]
470 uF [T495X477M010AT E200]	470 uF [T520D477M006AT E025]	470 uF [T520W477M006AT E055]	470 uF [T525D477M004AT E025]
470 uF [T510X477M006AT E030]	470 uF [T520D477M006AT E030]	470 uF [T520X477M006AT E010]	470 uF [T525D477M004AT E040]
470 uF [T513X477M006AH 6110]	470 uF [T520D477M2R5AT E006]	470 uF [T520X477M006AT E018]	470 uF [T525D477M2R5AT E025]
470 uF [T520C477M2R5AT E025]	470 uF [T520D477M2R5AT E007]	470 uF [T520X477M006AT E035]	470 uF [T528Z477M2R5AT E005]
470 uF [T520C477M2R5AT E045]	470 uF [T520D477M2R5AT E009]	470 uF [T520X477M006AT E040]	470 uF [T528Z477M2R5AT E009]
470 uF [T520D477M004AT E010]	470 uF [T520V477M002AT E040]	470 uF [T520Y477M006AT E010]	470 uF [T528Z477M2R5AT E012]
470 uF [T520D477M004AT E012]	470 uF [T520V477M2R5AT E007]	470 uF [T520Y477M006AT E015]	470 uF [T530D477M004AT E006]
470 uF [T520D477M004AT E015]	470 uF [T520V477M2R5AT E009]	470 uF [T520Y477M006AT E018]	470 uF [T530D477M004AT E010]

Multisim 14.0 Base Components

470 uF [T530D477M2R5AT E006]	5.1 nF [C0603C512K3HACT U]	5.6 nF [C0402C562K5RACT U]	5.6 nF [C0805C562K1RACT U]
470 uF [T530X477M006AT E004]	5.1 nF [C0603C512K5HACT U]	5.6 nF [C0603C562K1RACT U]	5.6 nF [C0805C562K2RACT U]
470 uF [T530X477M006AT E005]	5.1 nF [C0805C512K1GACT U]	5.6 nF [C0603C562K3GACT U]	5.6 nF [C0805C562K3GACT U]
470 uF [T530X477M006AT E006]	5.1 nF [C0805C512K1HACT U]	5.6 nF [C0603C562K3HACT U]	5.6 nF [C0805C562K3HACT U]
470 uF [T530X477M006AT E010]	5.1 nF [C0805C512K3HACT U]	5.6 nF [C0603C562K3RACT U]	5.6 nF [C0805C562K3RACT U]
470 uF [T530Y477M004AT E005]	5.1 nF [C0805C512K5HACT U]	5.6 nF [C0603C562K4RACT U]	5.6 nF [C0805C562K4RACT U]
470 uF [T530Y477M006AT E005]	5.1 nF [C1206C512K5GACT U]	5.6 nF [C0603C562K5HACT U]	5.6 nF [C0805C562K5HACT U]
470 uF [T543D477M2R5AT E007]	5.1 nF [C2220C512KBGAC TU]	5.6 nF [C0603C562K5RACT U]	5.6 nF [C0805C562K5RACT U]
47151-0001	5.1 nF [C2225C512KBGAC TU]	5.6 nF [C0603C562K8RACT U]	5.6 nF [C0805C562KARACT U]
47272-0001			
4Line_Bussed	5.6 nF	5.6 nF	5.6 nF
4Line_Isolated	[C0402C562K3RACT U]	[C0805C562K1GACT U]	[C1206C562K1RACT U]
4Line_Terminator	5.6 nF	5.6 nF	5.6 nF
4POS_ROTARY	[C0402C562K4RACT U]	[C0805C562K1HACT U]	[C1206C562K2RACT U]
4V_0.5W			

Multisim 14.0 Base Components

5.6 nF [C1206C562K5GACT U]	5.6 uF [C1206C565K8RACT U]	51 pF [C0805C510K2GACT U]	510 pF [C0402C511K1HACT U]
5.6 nF [C1206C562K5RACT U]	5.6 uF [C1206C565K9RACT U]	51 pF [C0805C510K5GACT U]	510 pF [C0402C511K3HACT U]
5.6 nF [C1206C562KARACT U]	5.6 uF [C1210C565K4PACT U]	51 pF [C0805C510KBGAC TU]	510 pF [C0402C511K5HACT U]
5.6 nF [C1210C562K5GACT U]	5_AMP 50_AMP	51 pF [C0805C510KCGAC TU]	510 pF [C0603C511K1HACT U]
5.6 nF [C1210C562K5RACT U]	50A02CH-TL-E 50A02CH-TL-H 50C02CH-TL-E	51 pF [C1206C510K5GACT U]	510 pF [C0603C511K3HACT U]
5.6 nF [C1210C562KARACT U]	51 mF [C0805C519K3GACT U]	51 pF [C1206C510KBGAC TU]	510 pF [C0603C511K5GACT U]
5.6 nF [C1812C562K2GACT U]	51 mF [C0805C519KBGAC TU]	51 pF [C1210C510KBGAC TU]	510 pF [C0603C511K5HACT U]
5.6 nF [C2220C562KBGAC TU]	51 pF [C0402C510K5GACT U]	51 pF [C1812C510KBGAC TU]	510 pF [C0603C511K8GACT U]
5.6 nF [C2225C562KBGAC TU]	51 pF [C0603C510K2GACT U]	51 pF [C1825C510KBGAC TU]	510 pF [C0805C511K5GACT U]
5.6 uF [C0805C565K9PACT U]	51 pF [C0603C510K5GACT U]	51 pF [C2220C510KBGAC TU]	510 pF [C1206C511K1GACT U]
5.6 uF [C1206C565K4RACT U]	51 pF [C0805C510K1GACT U]	51 pF [C2225C510KBGAC TU]	510 pF [C1206C511KBGAC TU]

Multisim 14.0 Base Components

510 pF [C1210C511KBGAC TU]	532903-6 534206-5 534237-3 534237-6 534237-8 5414337-1 555_VIRTUAL 5558067-1 56 mF [C0805C569KBGAC TU] 56 nF [C0402C563K4RACT U] 56 nF [C0402C563K8RACT U] 56 nF [C0402C563K9RACT U] 56 nF [C0603C563K3RACT U] 56 nF [C0603C563K4RACT U] 56 nF [C0603C563K5RACT U]	56 nF [C0805C563K1RACT U] 56 nF [C0805C563K2RACT U] 56 nF [C0805C563K3RACT U] 56 nF [C0805C563K4RACT U] 56 nF [C0805C563K5RACT U] 56 nF [C0805C563K8RACT U] 56 nF [C0805F563K3RACT U] 56 nF [C0805F563K4RACT U] 56 nF [C0805F563K5RACT U] 56 nF [C1206C563K1RACT U] 56 nF [C1206C563K3HACT U]	56 nF [C1206C563K3RACT U] 56 nF [C1206C563K5HACT U] 56 nF [C1206C563K5RACT U] 56 nF [C1206C563KARACT U] 56 nF [C1206C563M5UAC TU] 56 nF [C1206F563K1RACT U] 56 nF [C1206F563K3RACT U] 56 nF [C1206F563K4RACT U] 56 nF [C1206F563K5RACT U] 56 nF [C1210C563K1GACT U] 56 nF [C1210C563K1HACT U]
510 pF [C1812C511KBGAC TU]			
510 pF [C1825C511KBGAC TU]			
510 pF [C2220C511KBGAC TU]			
510 pF [C2225C511KBGAC TU]			
5103309-1			
5103309-5			
5103309-6			
5103309-7			
5103309-8			
5103310-1			
5103310-5			
5103310-6			
5103310-7			
5103310-8			
5-1814400-1			
5227222-3			
5227677-1			
532903-2			

Multisim 14.0 Base Components

56 nF [C1210C563K1RACT U]	56 nF [C1812C563K5HACT U]	56 pF [C0603C560K3GACT U]	56 pF [C1206C560KDGAC TU]
56 nF [C1210C563K2RACT U]	56 nF [C2220C563K1GACT U]	56 pF [C0603C560K5GACT U]	56 pF [C1210C560KBGAC TU]
56 nF [C1210C563K3HACT U]	56 nF [C2220C563K2GACT U]	56 pF [C0805C560K1GACT U]	56 pF [C1812C560KBGAC TU]
56 nF [C1210C563K5GACT U]	56 nF [C2220C563K5GACT U]	56 pF [C0805C560K2GACT U]	56 pF [C1812C560KHGAC TU]
56 nF [C1210C563K5HACT U]	56 pF [C0201C560K3GACT U]	56 pF [C0805C560K5GACT U]	56 pF [C1825C560KBGAC TU]
56 nF [C1210C563K5RACT U]	56 pF [C0201C560K8GACT U]	56 pF [C0805C560KBGAC TU]	56 pF [C2220C560KBGAC TU]
56 nF [C1210C563KARACT U]	56 pF [C0402C560K3GACT U]	56 pF [C0805C560KDGAC TU]	56 pF [C2225C560KBGAC TU]
56 nF [C1812C563K1GACT U]	56 pF [C0402C560K5GACT U]	56 pF [C1206C560K1GACT U]	56 pF [CA064C560K5GAC TU]
56 nF [C1812C563K1HACT U]	56 pF [C0402C560K8GACT U]	56 pF [C1206C560K2GACT U]	56 uF [A700D566M008AT E015]
56 nF [C1812C563K1RACT U]	56 pF [C0603C560K1GACT U]	56 pF [C1206C560K5GACT U]	56 uF [A700D566M008AT E018]
56 nF [C1812C563K5GACT U]	56 pF [C0603C560K2GACT U]	56 pF [C1206C560KBGAC TU]	56 uF [A700D566M010AT E015]

Multisim 14.0 Base Components

56 uF [A700D566M010AT E018]	560 nF [C1206C564K4RACT U]	560 nF [C1825C564K5RACT U]	560 pF [C0402C561K4RACT U]
56 uF [A700V566M006AT E018]	560 nF [C1206C564K5RACT U]	560 nF [C1825C564KARACT U]	560 pF [C0402C561K5HACT U]
56 uF [A700V566M006AT E025]	560 nF [C1206F564K4RACT U]	560 nF [C2220C564K1RACT U]	560 pF [C0402C561K5RACT U]
56 uF [A700V566M006AT E028]	560 nF [C1210C564K5RACT U]	560 nF [C2220C564K5RACT U]	560 pF [C0402C561K8RACT U]
56 uF [T520T566M2R5AT E040]	560 nF [C1210F564K3RACT U]	560 nF [C2220C564KARACT U]	560 pF [C0603C561K1HACT U]
56 uF [T520T566M2R5AT E070]	560 nF [C1210F564K4RACT U]	560 nF [C2225C564K5RACT U]	560 pF [C0603C561K1RACT U]
560 nF [C0603C564K8PACT U]	560 nF [C1210F564K5RACT U]	560 nF [C2225C564KARACT U]	560 pF [C0603C561K2RACT U]
560 nF [C0805C564K3RACT U]	560 nF [C1812C564K5RACT U]	560 pF [C0402C561K1HACT U]	560 pF [C0603C561K3HACT U]
560 nF [C0805C564K4RACT U]	560 nF [C1812F564K1RACT U]	560 pF [C0402C561K3GACT U]	560 pF [C0603C561K3RACT U]
560 nF [C0805C564K8RACT U]	560 nF [C1812F564K3RACT U]	560 pF [C0402C561K3HACT U]	560 pF [C0603C561K4RACT U]
560 nF [C1206C564K3RACT U]	560 nF [C1812F564K5RACT U]	560 pF [C0402C561K3RACT U]	560 pF [C0603C561K5GACT U]

Multisim 14.0 Base Components

560 pF [C0603C561K5HACT U]	560 pF [C1206C561K2GACT U]	571-0300	5LN01SS-TL-E
		571-0400	5LN01SS-TL-H
560 pF [C0603C561K5RACT U]	560 pF [C1206C561K5GACT U]	571-0500	5LN01S-TL-E
		571-0600	5POS_ROTARY
560 pF [C0603C561K8RACT U]	560 pF [C1206C561KBGAC TU]	571-0700	5V_1W
		5KP10A-E3/54	6.2 nF [C0603C622K3HACT U]
560 pF [C0805C561K1GACT U]	560 pF [C1210C561KBGAC TU]	5KP16A-E3/54	
		5KP18A-E3/54	6.2 nF [C0603C622K5HACT U]
560 pF [C0805C561K1RACT U]	560 pF [C1812C561KBGAC TU]	5KP22A-E3/54	
		5KP24A-E3/54	6.2 nF [C0805C622K1GACT U]
560 pF [C0805C561K2RACT U]	560 pF [C1825C561KBGAC TU]	5KP28A-E3/54	
		5KP30A-E3/54	6.2 nF [C0805C622K1HACT U]
560 pF [C0805C561K4RACT U]	560 pF [C2220C561KBGAC TU]	5KP33A-E3/54	
		5KP40A-E3/54	6.2 nF [C0805C622K3HACT U]
560 pF [C0805C561K5GACT U]	560 pF [C2225C561KBGAC TU]	5KP48A-E3/54	
		5KP58A-E3/54	6.2 nF [C0805C622K5HACT U]
560 pF [C0805C561K5RACT U]	560 pF [CA064C561K2RACT U]	5KP60A-E3/54	
		5KP85A-E3/54	6.2 nF [C2225C622KBGAC TU]
560 pF [C0805C561K8RACT U]	560 uF [T530D567M2R5AT E005]	5Line_Bussed	
		5Line_Isolated	6.2 nF [C0402C682K3RACT U]
560 pF [C1206C561K1GACT U]	5687169-9	5LN01C-TB-E	
	571-0100	5LN01C-TB-H	6.8 nF [C0402C682K4RACT U]
	571-0200	5LN01M-TL-E	
		5LN01M-TL-H	
		5LN01SP-AC	

Multisim 14.0 Base Components

6.8 nF [C0402C682K5RACT U]	6.8 nF [C0805C682K1GACT U]	6.8 nF [C1206C682K1RACT U]	6.8 nF [C1812C682K1GACT U]
6.8 nF [C0402C682K8RACT U]	6.8 nF [C0805C682K1HACT U]	6.8 nF [C1206C682K3GACT U]	6.8 nF [C1812C682K1RACT U]
6.8 nF [C0603C682K1RACT U]	6.8 nF [C0805C682K1RACT U]	6.8 nF [C1206C682K3HACT U]	6.8 nF [C1812C682K5GACT U]
6.8 nF [C0603C682K2RACT U]	6.8 nF [C0805C682K3GACT U]	6.8 nF [C1206C682K3RACT U]	6.8 nF [C1812C682K5RACT U]
6.8 nF [C0603C682K3GACT U]	6.8 nF [C0805C682K3HACT U]	6.8 nF [C1206C682K5HACT U]	6.8 nF [C2220C682K2GACT U]
6.8 nF [C0603C682K3HACT U]	6.8 nF [C0805C682K3RACT U]	6.8 nF [C1206C682K5RACT U]	6.8 nF [C2225C682KBGAC TU]
6.8 nF [C0603C682K3RACT U]	6.8 nF [C0805C682K4RACT U]	6.8 nF [C1210C682K1GACT U]	6.8 nF [CDR06BP682BKSM]
6.8 nF [C0603C682K4RACT U]	6.8 nF [C0805C682K5GACT U]	6.8 nF [C1210C682K1RACT U]	6.8 uF [A700V685M016AT E070]
6.8 nF [C0603C682K5HACT U]	6.8 nF [C0805C682K5HACT U]	6.8 nF [C1210C682K5GACT U]	6.8 uF [C0805C685K8PACT U]
6.8 nF [C0603C682K5RACT U]	6.8 nF [C0805C682K5RACT U]	6.8 nF [C1210C682K5RACT U]	6.8 uF [C0805C685K9PACT U]
6.8 nF [C0603C682K8RACT U]	6.8 nF [C1206C682K1HACT U]	6.8 nF [C1210C682KARACT U]	6.8 uF [C1206C685K4PACT U]

Multisim 14.0 Base Components

6.8 uF [C1206C685K4RACT U]	6.8 uF [T489B685M010AT E3K0]	6.8 uF [T491D685M050AT]	6.8 uF [T494B685M020AT]
6.8 uF [C1206C685K8RACT U]	6.8 uF [T491A685M004AT]	6.8 uF [T491S685M004AT]	6.8 uF [T494B685M025AT]
6.8 uF [C1206C685K9PACT U]	6.8 uF [T491A685M006AT]	6.8 uF [T491S685M006AT]	6.8 uF [T494C685M016AT]
6.8 uF [C1206C685K9RACT U]	6.8 uF [T491A685M010AT]	6.8 uF [T491S685M010AT]	6.8 uF [T494C685M020AT]
6.8 uF [C1206C685K9RACT U]	6.8 uF [T491A685M016AT]	6.8 uF [T491T685M010AT]	6.8 uF [T494C685M025AT]
6.8 uF [C1210C685K3PACT U]	6.8 uF [T491A685M020AT]	6.8 uF [T491U685M020AT]	6.8 uF [T494C685M035AT]
6.8 uF [C1210C685K4PACT U]	6.8 uF [T491B685M006AT]	6.8 uF [T491X685M050AT]	6.8 uF [T494D685M035AT]
6.8 uF [C1210C685K4PACT U]	6.8 uF [T491B685M010AT]	6.8 uF [T494A685M004AT]	6.8 uF [T494D685M050AT]
6.8 uF [C1210C685K8PACT U]	6.8 uF [T491B685M016AT]	6.8 uF [T494A685M006AT]	6.8 uF [T494S685M004AT]
6.8 uF [C1210C685M4VAC TU]	6.8 uF [T491B685M025AT]	6.8 uF [T494A685M010AT]	6.8 uF [T494S685M006AT]
6.8 uF [T419B685M006AH 4250]	6.8 uF [T491C685M016AT]	6.8 uF [T494A685M016AT]	6.8 uF [T494S685M010AT]
6.8 uF [T419C685M010AH 4250]	6.8 uF [T491C685M020AT]	6.8 uF [T494A685M020AT]	6.8 uF [T494T685M010AT]
6.8 uF [T419C685M010AH 4250]	6.8 uF [T491C685M025AT]	6.8 uF [T494B685M006AT]	6.8 uF [T494U685M020AT]
6.8 uF [T429D685M006AH 4250]	6.8 uF [T491C685M035AT]	6.8 uF [T494B685M010AT]	6.8 uF [T494X685M050AT]
	6.8 uF [T491D685M035AT]	6.8 uF [T494B685M016AT]	

Multisim 14.0 Base Components

6.8 uF [T495C685M025AT E400]	6.8 uF [T521D685M050AT E090]	62 pF [C1825C620KBGAC TU]	620 pF [C1210C621KBGAC TU]
6.8 uF [T495C685M025AT E500]	6.8 uF [T521V685M050AT E090]	62 pF [C2220C620KBGAC TU]	620 pF [C1812C621KBGAC TU]
6.8 uF [T495D685M035AT E150]	61729-0010BLF 62 mF [C0805C629KBGAC TU]	62 pF [C2225C620KBGAC TU]	620 pF [C1825C621KBGAC TU]
6.8 uF [T495D685M050AT E190]	62 pF [C0402C620K3GACT U]	620 pF [C0402C621K1HACT U]	620 pF [C2220C621KBGAC TU]
6.8 uF [T495D685M050AT E200]	62 pF [C0402C620K5GACT U]	620 pF [C0402C621K3HACT U]	620 pF [C2225C621KBGAC TU]
6.8 uF [T495D685M050AT E300]	62 pF [C0603C620K5GACT U]	620 pF [C0402C621K5HACT U]	640455-5 640455-8
6.8 uF [T497B685M010AT 6110]	62 pF [C0805C620KBGAC TU]	620 pF [C0603C621K1HACT U]	68 mF [C0402C689K8GACT U]
6.8 uF [T498A685M016AT E2K6]	62 pF [C1206C620KBGAC TU]	620 pF [C0603C621K3HACT U]	68 mF [C0805C689KBGAC TU]
6.8 uF [T498B685M016AT E1K8]	62 pF [C1206C620KDGAC TU]	620 pF [C0603C621K5GACT U]	68 mF [C1206C689K2GACT U]
6.8 uF [T498D685M035AT E900]	62 pF [C1210C620KBGAC TU]	620 pF [C0603C621K5HACT U]	68 nF [C0402C683K4RACT U]
6.8 uF [T499C685M020AT E1K9]	62 pF [C1812C620KBGAC TU]	620 pF [C0805C621K5GACT U]	68 nF [C0402C683K8PACT U]

Multisim 14.0 Base Components

68 nF [C0402C683K8RACT U]	68 nF [C0805C683K4RACT U]	68 nF [C1206C683K5HACT U]	68 nF [C1210C683K2RACT U]
68 nF [C0402C683K9PACT U]	68 nF [C0805C683K5RACT U]	68 nF [C1206C683K5RACT U]	68 nF [C1210C683K3GACT U]
68 nF [C0402C683K9RACT U]	68 nF [C0805C683K8RACT U]	68 nF [C1206C683KARACT U]	68 nF [C1210C683K3HACT U]
68 nF [C0603C683K3RACT U]	68 nF [C0805C683M5UAC TU]	68 nF [C1206C683M5UAC TU]	68 nF [C1210C683K5GACT U]
68 nF [C0603C683K4RACT U]	68 nF [C0805F683K3RACT U]	68 nF [C1206F683K1RACT U]	68 nF [C1210C683K5HACT U]
68 nF [C0603C683K5RACT U]	68 nF [C0805F683K4RACT U]	68 nF [C1206F683K3RACT U]	68 nF [C1210C683K5RACT U]
68 nF [C0603C683K8RACT U]	68 nF [C0805F683K5RACT U]	68 nF [C1206F683K4RACT U]	68 nF [C1210C683KARACT U]
68 nF [C0603C683K9RACT U]	68 nF [C1206C683K1RACT U]	68 nF [C1206F683K5RACT U]	68 nF [C1210F683K2RACT U]
68 nF [C0603C683M3VAC TU]	68 nF [C1206C683K2RACT U]	68 nF [C1210C683K1GACT U]	68 nF [C1812C683K1GACT U]
68 nF [C0805C683K1RACT U]	68 nF [C1206C683K3GACT U]	68 nF [C1210C683K1HACT U]	68 nF [C1812C683K1HACT U]
68 nF [C0805C683K3RACT U]	68 nF [C1206C683K3HACT U]	68 nF [C1210C683K1RACT U]	68 nF [C1812C683K1RACT U]

Multisim 14.0 Base Components

68 nF [C1812C683K2RACT U]	68 pF [C0402C680K5GACT U]	68 pF [C1206C680K2GACT U]	68 pF [CA064C680K8GAC TU]
68 nF [C1812C683K5GACT U]	68 pF [C0402C680K8GACT U]	68 pF [C1206C680K5GACT U]	68 pF [CDR01BP680BKSM]
68 nF [C1812C683K5HACT U]	68 pF [C0603C680K2GACT U]	68 pF [C1206C680KBGAC TU]	68 uF [A700D686M008AT E015]
68 nF [C1812C683K5RACT U]	68 pF [C0603C680K3GACT U]	68 pF [C1206C680KDGAC TU]	68 uF [A700D686M008AT E018]
68 nF [C2220C683K1GACT U]	68 pF [C0603C680K4GACT U]	68 pF [C1206C680KGGAC TU]	68 uF [A700D686M010AT E015]
68 nF [C2220C683K2GACT U]	68 pF [C0603C680K5GACT U]	68 pF [C1210C680KBGAC TU]	68 uF [A700D686M010AT E018]
68 nF [C2220C683K5GACT U]	68 pF [C0805C680K1GACT U]	68 pF [C1812C680KBGAC TU]	68 uF [A700V686M006AT E018]
68 nF [CA064C683K4RACT U]	68 pF [C0805C680K2GACT U]	68 pF [C1825C680KBGAC TU]	68 uF [A700V686M006AT E025]
68 nF [CDR05BX683BKSM]	68 pF [C0805C680K5GACT U]	68 pF [C2220C680KBGAC TU]	68 uF [A700V686M006AT E028]
68 pF [C0201C680K3GACT U]	68 pF [C0805C680KBGAC TU]	68 pF [C2225C680KBGAC TU]	68 uF [T419G686M010AH 4250]
68 pF [C0402C680K3GACT U]	68 pF [C1206C680K1GACT U]	68 pF [CA064C680K5GAC TU]	68 uF [T491A686M004AT] 68 uF [T491A686M006AT]

Multisim 14.0 Base Components

68 uF [T491B686M004AT]	68 uF [T491U686M004AT]	68 uF [T494C686M010AT]	68 uF [T494V686M016AT]
68 uF [T491B686M006AT]	68 uF [T491U686M006AT]	68 uF [T494C686M016AT]	68 uF [T494X686M020AT]
68 uF [T491B686M010AT]	68 uF [T491U686M010AT]	68 uF [T494D686M004AT]	68 uF [T494X686M025AT]
68 uF [T491C686M004AT]	68 uF [T491U686M010AT]	68 uF [T494D686M006AT]	68 uF [T495B686M010AT E900]
68 uF [T491C686M006AT]	68 uF [T491V686M010AT]	68 uF [T494D686M010AT]	68 uF [T495C686M010AT E225]
68 uF [T491C686M010AT]	68 uF [T491V686M016AT]	68 uF [T494D686M010AT]	68 uF [T495D686M006AT E175]
68 uF [T491C686M016AT]	68 uF [T491X686M020AT]	68 uF [T494D686M016AT]	68 uF [T495D686M010AT E070]
68 uF [T491D686M004AT]	68 uF [T491X686M025AT]	68 uF [T494D686M020AT]	68 uF [T495D686M010AT E090]
68 uF [T491D686M006AT]	68 uF [T494A686M004AT]	68 uF [T494D686M025AT]	68 uF [T495D686M010AT E150]
68 uF [T491D686M010AT]	68 uF [T494B686M004AT]	68 uF [T494U686M004AT]	68 uF [T495D686M016AT E070]
68 uF [T491D686M016AT]	68 uF [T494B686M006AT]	68 uF [T494U686M006AT]	68 uF [T495D686M016AT E100]
68 uF [T491D686M020AT]	68 uF [T494C686M004AT]	68 uF [T494U686M010AT]	68 uF [T495D686M016AT E150]
68 uF [T491D686M025AT]	68 uF [T494C686M006AT]	68 uF [T494V686M010AT]	

Multisim 14.0 Base Components

68 uF [T495D686M020AT E070]	68 uF [T513X686M025AH 6110]	68 uF [T520B686M006AT E070]	68 uF [T520V686M010AT E045]
68 uF [T495D686M020AT E150]	68 uF [T520A686M006AT E150]	68 uF [T520C686M006AT E100]	68 uF [T520V686M010AT E060]
68 uF [T495D686M025AT E150]	68 uF [T520A686M2R5AT E070]	68 uF [T520C686M010AT E045]	68 uF [T520V686M010AT E100]
68 uF [T495D686M025AT E200]	68 uF [T520A686M2R5AT E080]	68 uF [T520T686M004AT E070]	68 uF [T520W686M010AT E040]
68 uF [T495V686M010AT E100]	68 uF [T520B686M004AT E025]	68 uF [T520T686M006AT E070]	68 uF [T521D686M016AT E050]
68 uF [T495V686M010AT E140]	68 uF [T520B686M004AT E035]	68 uF [T520T686M006AT E150]	68 uF [T521V686M016AT E050]
68 uF [T495V686M016AT E300]	68 uF [T520B686M004AT E040]	68 uF [T520U686M004AT E055]	68 uF [T521V686M016AT E090]
68 uF [T495X686M010AT E150]	68 uF [T520B686M004AT E070]	68 uF [T520U686M006AT E055]	68 uF [T525B686M004AT E080]
68 uF [T495X686M020AT E150]	68 uF [T520B686M006AT E025]	68 uF [T520U686M006AT E070]	68 uF [T525B686M006AT E080]
68 uF [T495X686M025AT E125]	68 uF [T520B686M006AT E035]	68 uF [T520V686M010AT E025]	68 uF [T525T686M004AT E080]
68 uF [T495X686M025AT E200]	68 uF [T520B686M006AT E040]	68 uF [T520V686M010AT E040]	68 uF [T543U686M006AT E055]

Multisim 14.0 Base Components

680 nF [C0603C684K4PACT U]	680 nF [C1206C684M4VAC TU]	680 nF [C1812C684M5UAC TU]	680 nF [C2225C684K5RACT U]
680 nF [C0603C684K8PACT U]	680 nF [C1206F684K4RACT U]	680 nF [C1812F684K1RACT U]	680 nF [C2225C684KARACT U]
680 nF [C0805C684K3PACT U]	680 nF [C1210C684K3RACT U]	680 nF [C1812F684K3RACT U]	680 nF [T491A684M020AT]
680 nF [C0805C684K4RACT U]	680 nF [C1210C684K4RACT U]	680 nF [C1812F684K5RACT U]	680 nF [T491A684M025AT]
680 nF [C0805C684K8RACT U]	680 nF [C1210C684K5RACT U]	680 nF [C1825C684K1RACT U]	680 nF [T491A684M035AT]
680 nF [C0805C684M4VAC TU]	680 nF [C1210C684M3VAC TU]	680 nF [C1825C684K5RACT U]	680 nF [T491B684M050AT]
680 nF [C1206C684K3RACT U]	680 nF [C1210C684M5VAC TU]	680 nF [C1825C684KARACT U]	680 nF [T491C684M050AT]
680 nF [C1206C684K4RACT U]	680 nF [C1210F684K3RACT U]	680 nF [C2220C684K1RACT U]	680 nF [T494A684M020AT]
680 nF [C1206C684K5RACT U]	680 nF [C1210F684K4RACT U]	680 nF [C2220C684K5RACT U]	680 nF [T494A684M035AT]
680 nF [C1206C684K8RACT U]	680 nF [C1210F684K5RACT U]	680 nF [C2220C684KARACT U]	680 nF [T494B684M035AT]
680 nF [C1206C684M3VAC TU]	680 nF [C1812C684K5RACT U]	680 nF [C2225C684K1RACT U]	680 nF [T494C684M050AT]

Multisim 14.0 Base Components

680 nF [T496C684M050AT 6110]	680 pF [C0603C681K3GACT U]	680 pF [C0805C681K4RACT U]	680 pF [C1825C681KBGAC TU]
680 pF [C0402C681K1HACT U]	680 pF [C0603C681K3HACT U]	680 pF [C0805C681K5GACT U]	680 pF [C2220C681KBGAC TU]
680 pF [C0402C681K3GACT U]	680 pF [C0603C681K3RACT U]	680 pF [C0805C681K5RACT U]	680 pF [C2220C681KZGACT U]
680 pF [C0402C681K3HACT U]	680 pF [C0603C681K4RACT U]	680 pF [C1206C681K1GACT U]	680 pF [C2225C681KBGAC TU]
680 pF [C0402C681K3RACT U]	680 pF [C0603C681K5GACT U]	680 pF [C1206C681K2GACT U]	680 uF [T491D687M004AT]
680 pF [C0402C681K4RACT U]	680 pF [C0603C681K5HACT U]	680 pF [C1206C681K5GACT U]	680 uF [T491E687M006AT]
680 pF [C0402C681K5HACT U]	680 pF [C0603C681K5RACT U]	680 pF [C1206C681KCGAC TU]	680 uF [T491X687M004AT]
680 pF [C0402C681K5RACT U]	680 pF [C0805C681K1GACT U]	680 pF [C1210C681KBGAC TU]	680 uF [T494D687M004AT]
680 pF [C0603C681K1HACT U]	680 pF [C0805C681K1RACT U]	680 pF [C1210C681KCGAC TU]	680 uF [T494E687M006AT]
680 pF [C0603C681K1RACT U]	680 pF [C0805C681K2RACT U]	680 pF [C1210C681KDGAC TU]	680 uF [T510E687M006AT E012]
680 pF [C0603C681K2RACT U]	680 pF [C0805C681K4GACT U]	680 pF [C1812C681KBGAC TU]	680 uF [T510E687M006AT E023]

Multisim 14.0 Base Components

680 uF [T510X687M004AT E030]	680 uF [T520D687M004AT E025]	680 uF [T520Y687M2R5AT E025]	680 uF [T530Y687M004AT E005]
680 uF [T510X687M006AT E023]	680 uF [T520D687M2R5AT E010]	680 uF [T525D687M003AT E025]	680 uF [T530Y687M2R5AT E006]
680 uF [T513E687M006AH 6110]	680 uF [T520D687M2R5AT E015]	680 uF [T525D687M2R5AT E025]	680 uF [T543X687M004AT E015]
680 uF [T513E687M006AH 6120]	680 uF [T520D687M2R5AT E040]	680 uF [T530D687M003AT E010]	690-009-521-900 6F6 6J5 6Line_Bussed 6Line_Isolated 6N1136 6N1136-X006 6N1136-X009T 6N136 6N136-000E 6N136-020E 6N136-060E 6N136-300E 6N136-320E 6N136-360E 6N136-X001 6N136-X006 6N136-X007T
680 uF [T513X687M004AH 6110]	680 uF [T520X687M004AT E010]	680 uF [T530D687M2R5AT E006]	
680 uF [T513X687M006AH 6110]	680 uF [T520X687M004AT E015]	680 uF [T530D687M2R5AT E010]	
680 uF [T513X687M006AH 6120]	680 uF [T520X687M004AT E035]	680 uF [T530X687M004AT E004]	
680 uF [T520D687M003AT E015]	680 uF [T520Y687M004AT E010]	680 uF [T530X687M004AT E006]	
680 uF [T520D687M003AT E040]	680 uF [T520Y687M004AT E015]	680 uF [T530X687M004AT E010]	
680 uF [T520D687M004AT E012]	680 uF [T520Y687M004AT E025]	680 uF [T530X687M006AT E010]	
680 uF [T520D687M004AT E015]	680 uF [T520Y687M2R5AT E015]	680 uF [T530X687M006AT E018]	

Multisim 14.0 Base Components

6N136-X009T	7.5 nF	7410N	74173N
6N136-X016	[C0805C752K5GACT U]	74116N	74174N
6N136-X017T	7.5 nF	74125N	74175N
6N136-X019T	[C0805C752K5HACT U]	74126N	7417N
6N137	7.5 nF	7412N	74181J
6N137-X006	[C1206C752K1HACT U]	74132N	74181N
6N137-X007T		74145N	74190N
6N139-000E	7.5 nF	74147N	74191N
6N139-020E	[C1206C752K3HACT U]	74148N	74192N
6N139-060E	7.5 nF	7414N	74194N
6N139-300E	[C1206C752K5HACT U]	74150N	74195N
6N139-320E	7.5 nF	74151N	74198N
6N139-360E	[CDR34BP752AKSM]	74153N	74199N
6POS_ROTARY	73391-0060	74154N	741-DIV
6SF5	7400N	74155N	7420N
7.5 nF	7402N	74156N	7422N
[C0603C752K3HACT U]	7403N	74157N	74251J
7.5 nF	7404N	74159N	74251N
[C0805C752K1GACT U]	7405N	74160N	7425N
7.5 nF	7406N	74162N	7426N
[C0805C752K1HACT U]	7407N	74163N	74279N
7.5 nF	7408N	74164N	7427N
[C0805C752K3HACT U]	7409N	74165N	7428N
	74107N	74166N	74290N
	74109N	7416N	74293N

Multisim 14.0 Base Components

74298N	7475N	74HC03N_4V	74HC09N_6V
7430N	7476N	74HC03N_6V	74HC107D_2V
74320-1004	7477W	74HC04D_2V	74HC107D_4V
74320-3004	7486N	74HC04D_4V	74HC107D_6V
74320-4004	749070-9	74HC04D_6V	74HC107N_2V
74320-5000	7490N	74HC04N_2V	74HC107N_4V
7432N	7491N	74HC04N_4V	74HC107N_6V
7433N	7492N	74HC04N_6V	74HC109D_2V
74365N	7493N	74HC05D_2V	74HC109D_4V
74367N	74HC00D_2V	74HC05D_4V	74HC109D_6V
74368N	74HC00D_4V	74HC05D_6V	74HC109N_2V
7437N	74HC00D_6V	74HC05N_2V	74HC109N_4V
7438N	74HC00N_2V	74HC05N_4V	74HC109N_6V
74393N	74HC00N_4V	74HC05N_6V	74HC10D_2V
7439N	74HC00N_6V	74HC08D_2V	74HC10D_4V
7440N	74HC02D_2V	74HC08D_4V	74HC10D_6V
7442N	74HC02D_4V	74HC08D_6V	74HC10N_2V
7445N	74HC02D_6V	74HC08N_2V	74HC10N_4V
7446N	74HC02N_2V	74HC08N_4V	74HC10N_6V
7447N	74HC02N_4V	74HC08N_6V	74HC112D_2V
7451N	74HC02N_6V	74HC09D_2V	74HC112D_4V
7454N	74HC03D_2V	74HC09D_4V	74HC112D_6V
7472N	74HC03D_4V	74HC09D_6V	74HC112N_2V
7473N	74HC03D_6V	74HC09N_2V	74HC112N_4V
7474N	74HC03N_2V	74HC09N_4V	74HC112N_6V

Multisim 14.0 Base Components

74HC113D_2V	74HC133D_4V	74HC139N_6V	74HC153DW_2V
74HC113D_4V	74HC133D_4V	74HC147N_2V	74HC153DW_4V
74HC113D_6V	74HC133D_6V	74HC147N_4V	74HC153DW_6V
74HC113N_2V	74HC133N_2V	74HC147N_6V	74HC153N_2V
74HC113N_4V	74HC133N_4V	74HC148DW_2V	74HC153N_4V
74HC113N_6V	74HC133N_6V	74HC148DW_4V	74HC153N_6V
74HC114D_2V	74HC137D_2V	74HC148DW_6V	74HC154DW_2V
74HC114D_4V	74HC137D_4V	74HC148N_2V	74HC154DW_4V
74HC114D_6V	74HC137D_6V	74HC148N_4V	74HC154DW_6V
74HC114N_2V	74HC137N_2V	74HC148N_6V	74HC154NT_2V
74HC114N_4V	74HC137N_4V	74HC151D_2V	74HC154NT_4V
74HC114N_6V	74HC137N_6V	74HC151D_4V	74HC154NT_6V
74HC11D_2V	74HC138D_2V	74HC151D_6V	74HC157D_2V
74HC11D_4V	74HC138D_4V	74HC151N_2V	74HC157D_4V
74HC11D_6V	74HC138D_4V	74HC151N_4V	74HC157D_6V
74HC11N_2V	74HC138D_6V	74HC151N_6V	74HC157N_2V
74HC11N_4V	74HC138N_2V	74HC152D_2V	74HC157N_4V
74HC11N_6V	74HC138N_4V	74HC152D_4V	74HC157N_6V
74HC125N_2V	74HC138N_4V	74HC152D_6V	74HC158D_2V
74HC125N_4V	74HC138N_6V	74HC152N_2V	74HC158D_4V
74HC125N_6V	74HC139DW_2V	74HC152N_4V	74HC158D_6V
74HC126N_2V	74HC139DW_4V	74HC152N_6V	74HC158N_2V
74HC126N_4V	74HC139DW_6V	74HC153D_2V	74HC158N_4V
74HC126N_6V	74HC139N_2V	74HC153D_4V	74HC158N_6V
74HC133D_2V	74HC139N_4V	74HC153D_6V	74HC160D_2V

Multisim 14.0 Base Components

74HC160D_4V	74HC165N_6V	74HC190D_2V	74HC20D_4V
74HC160D_6V	74HC166D_2V	74HC190D_4V	74HC20D_6V
74HC160N_2V	74HC166D_4V	74HC190D_6V	74HC20N_2V
74HC160N_4V	74HC166D_6V	74HC190N_2V	74HC20N_4V
74HC160N_6V	74HC166N_2V	74HC190N_4V	74HC20N_6V
74HC162D_2V	74HC166N_4V	74HC190N_6V	74HC21D_2V
74HC162D_4V	74HC166N_6V	74HC191D_2V	74HC21D_4V
74HC162D_6V	74HC173D_2V	74HC191D_4V	74HC21D_6V
74HC162N_2V	74HC173D_4V	74HC191D_6V	74HC21N_2V
74HC162N_4V	74HC173D_6V	74HC191N_2V	74HC21N_4V
74HC162N_6V	74HC173N_2V	74HC191N_4V	74HC21N_6V
74HC163D_2V	74HC173N_4V	74HC191N_6V	74HC240DW_2V
74HC163D_4V	74HC173N_6V	74HC192D_2V	74HC240DW_4V
74HC163D_6V	74HC174D_2V	74HC192D_4V	74HC240DW_6V
74HC163N_2V	74HC174D_4V	74HC192D_6V	74HC240N_2V
74HC163N_4V	74HC174D_6V	74HC192N_2V	74HC240N_4V
74HC163N_6V	74HC174N_2V	74HC192N_4V	74HC240N_6V
74HC164N_2V	74HC174N_4V	74HC192N_6V	74HC241DW_2V
74HC164N_4V	74HC174N_6V	74HC194N_2V	74HC241DW_4V
74HC164N_6V	74HC175D_2V	74HC194N_4V	74HC241DW_6V
74HC165D_2V	74HC175D_4V	74HC194N_6V	74HC241N_2V
74HC165D_4V	74HC175D_6V	74HC195N_2V	74HC241N_4V
74HC165D_6V	74HC175N_2V	74HC195N_4V	74HC241N_6V
74HC165N_2V	74HC175N_4V	74HC195N_6V	74HC244_4V
74HC165N_4V	74HC175N_6V	74HC20D_2V	74HC244DW_2V

Multisim 14.0 Base Components

74HC244DW_4V	74HC258D_6V	74HC280N_2V	74HC365D_4V
74HC244DW_6V	74HC258N_2V	74HC280N_4V	74HC365D_6V
74HC244N_2V	74HC258N_4V	74HC280N_6V	74HC365N_2V
74HC244N_4V	74HC258N_6V	74HC283D_2V	74HC365N_4V
74HC244N_6V	74HC266D_2V	74HC283D_4V	74HC365N_6V
74HC251D_2V	74HC266D_4V	74HC283D_6V	74HC366D_2V
74HC251D_4V	74HC266D_6V	74HC283N_2V	74HC366D_6V
74HC251D_6V	74HC266N_2V	74HC283N_4V	74HC366N_2V
74HC251N_2V	74HC266N_4V	74HC283N_6V	74HC366N_6V
74HC251N_4V	74HC266N_6V	74HC298N_2V	74HC367D_2V
74HC251N_6V	74HC273DW_2V	74HC298N_4V	74HC367D_4V
74HC253D_2V	74HC273DW_4V	74HC298N_6V	74HC367D_6V
74HC253D_4V	74HC273DW_6V	74HC30D_2V	74HC367N_2V
74HC253D_6V	74HC273N_2V	74HC30D_4V	74HC367N_4V
74HC253N_2V	74HC273N_4V	74HC30D_6V	74HC367N_6V
74HC253N_4V	74HC273N_6V	74HC30N_2V	74HC368D_2V
74HC253N_6V	74HC27D_2V	74HC30N_4V	74HC368D_4V
74HC257D_2V	74HC27D_4V	74HC30N_6V	74HC368D_6V
74HC257D_4V	74HC27D_6V	74HC32D_2V	74HC368N_2V
74HC257D_6V	74HC27N_2V	74HC32D_4V	74HC368N_4V
74HC257N_2V	74HC27N_4V	74HC32D_6V	74HC368N_6V
74HC257N_4V	74HC27N_6V	74HC32N_2V	74HC373DW_2V
74HC257N_6V	74HC280D_2V	74HC32N_4V	74HC373DW_4V
74HC258D_2V	74HC280D_4V	74HC32N_6V	74HC373DW_6V
74HC258D_4V	74HC280D_6V	74HC365D_2V	74HC373N_2V

Multisim 14.0 Base Components

74HC373N_4V	74HC378N_6V	74HC73D_2V	74HC77D_4V
74HC373N_6V	74HC379D_2V	74HC73D_4V	74HC77D_6V
74HC374DW_2V	74HC379D_4V	74HC73D_6V	74HC77N_2V
74HC374DW_4V	74HC379D_6V	74HC73N_2V	74HC77N_4V
74HC374DW_6V	74HC379J_2V	74HC73N_4V	74HC77N_6V
74HC374N_2V	74HC379J_4V	74HC73N_6V	74HC78D_2V
74HC374N_4V	74HC379J_6V	74HC74D_2V	74HC78D_4V
74HC374N_6V	74HC379N_2V	74HC74D_4V	74HC78D_6V
74HC375D_2V	74HC379N_4V	74HC74D_6V	74HC78N_2V
74HC375D_4V	74HC379N_6V	74HC74N_2V	74HC78N_4V
74HC375D_6V	74HC393N_2V	74HC74N_4V	74HC78N_6V
74HC375N_2V	74HC393N_4V	74HC74N_6V	74HC86D_2V
74HC375N_4V	74HC393N_6V	74HC75D_2V	74HC86D_4V
74HC375N_6V	74HC42D_2V	74HC75D_4V	74HC86D_6V
74HC377DW_2V	74HC42D_4V	74HC75D_6V	74HC86N_2V
74HC377DW_4V	74HC42D_6V	74HC75N_2V	74HC86N_4V
74HC377DW_6V	74HC42N_2V	74HC75N_4V	74HC86N_6V
74HC377N_2V	74HC42N_4V	74HC75N_6V	74LS00D
74HC377N_4V	74HC42N_6V	74HC76D_2V	74LS00D
74HC377N_6V	74HC51D_2V	74HC76D_4V	74LS00N
74HC378D_2V	74HC51D_4V	74HC76D_6V	74LS00N
74HC378D_4V	74HC51D_6V	74HC76N_2V	74LS02D
74HC378D_6V	74HC51N_2V	74HC76N_4V	74LS02D
74HC378N_2V	74HC51N_4V	74HC76N_6V	74LS02N
74HC378N_4V	74HC51N_6V	74HC77D_2V	74LS02N

Multisim 14.0 Base Components

74LS03D	74LS107N	74LS125D	74LS147D
74LS03D	74LS109D	74LS125D	74LS147N
74LS03N	74LS109D	74LS125N	74LS147N
74LS03N	74LS109N	74LS126D	74LS148D
74LS04D	74LS109N	74LS126D	74LS148D
74LS04D	74LS10D	74LS126N	74LS148N
74LS04N	74LS10D	74LS12D	74LS148N
74LS04N	74LS10N	74LS12D	74LS14D
74LS05D	74LS10N	74LS12N	74LS14N
74LS05D	74LS112D	74LS12N	74LS151D
74LS05N	74LS112D	74LS132D	74LS151D
74LS05N	74LS112N	74LS132N	74LS151N
74LS08D	74LS112N	74LS138D	74LS151N
74LS08D	74LS113D	74LS138D	74LS153D
74LS08J	74LS113D	74LS138N	74LS153D
74LS08J	74LS113N	74LS138N	74LS153N
74LS08N	74LS113N	74LS139D	74LS153N
74LS08N	74LS114D	74LS139D	74LS155D
74LS09D	74LS114D	74LS139N	74LS155D
74LS09D	74LS114N	74LS139N	74LS155N
74LS09N	74LS114N	74LS145D	74LS155N
74LS09N	74LS11D	74LS145D	74LS156D
74LS107D	74LS11D	74LS145N	74LS156D
74LS107D	74LS11N	74LS145N	74LS156N
74LS107N	74LS11N	74LS147D	74LS156N

Multisim 14.0 Base Components

74LS157D	74LS164D	74LS175N	74LS195N
74LS157D	74LS164N	74LS175N	74LS20D
74LS157N	74LS164N	74LS181DW	74LS20D
74LS157N	74LS165D	74LS181DW	74LS20N
74LS158D	74LS165D	74LS181N	74LS20N
74LS158D	74LS165N	74LS181N	74LS21D
74LS158N	74LS165N	74LS190D	74LS21D
74LS158N	74LS166D	74LS190D	74LS21N
74LS15D	74LS166D	74LS190N	74LS21N
74LS15D	74LS166N	74LS190N	74LS22D
74LS15N	74LS166N	74LS191D	74LS22D
74LS15N	74LS169D	74LS191D	74LS22N
74LS160D	74LS169D	74LS191N	74LS22N
74LS160D	74LS169N	74LS191N	74LS240DW
74LS160N	74LS169N	74LS192D	74LS240DW
74LS160N	74LS173D	74LS192D	74LS240N
74LS162D	74LS173D	74LS192N	74LS240N
74LS162D	74LS173N	74LS192N	74LS241DW
74LS162N	74LS173N	74LS194D	74LS241DW
74LS162N	74LS174D	74LS194D	74LS241N
74LS163D	74LS174D	74LS194N	74LS241N
74LS163D	74LS174N	74LS194N	74LS244DW
74LS163N	74LS174N	74LS195D	74LS244N
74LS163N	74LS175D	74LS195D	74LS251D
74LS164D	74LS175D	74LS195N	74LS251D

Multisim 14.0 Base Components

74LS251N	74LS273N	74LS298N	74LS365N
74LS251N	74LS279D	74LS298N	74LS367D
74LS253D	74LS279N	74LS30D	74LS367D
74LS253D	74LS27D	74LS30N	74LS367N
74LS253N	74LS27D	74LS30N	74LS367N
74LS253N	74LS27N	74LS32D	74LS368D
74LS257D	74LS27N	74LS32D	74LS368D
74LS257D	74LS280D	74LS32N	74LS368N
74LS257N	74LS280D	74LS32N	74LS368N
74LS257N	74LS280N	74LS33D	74LS373DW
74LS258D	74LS280N	74LS33D	74LS373DW
74LS258D	74LS28D	74LS33N	74LS373N
74LS258N	74LS28D	74LS33N	74LS373N
74LS258N	74LS28N	74LS348D	74LS374DW
74LS266D	74LS28N	74LS348N	74LS374DW
74LS266D	74LS290D	74LS352D	74LS374N
74LS266N	74LS290D	74LS352D	74LS374N
74LS266N	74LS290N	74LS352N	74LS375D
74LS26D	74LS290N	74LS352N	74LS375N
74LS26D	74LS293D	74LS353D	74LS377DW
74LS26N	74LS293D	74LS353D	74LS377DW
74LS26N	74LS293N	74LS353N	74LS377N
74LS273DW	74LS293N	74LS365D	74LS377N
74LS273DW	74LS298D	74LS365D	74LS378D
74LS273N	74LS298D	74LS365N	74LS378D

Multisim 14.0 Base Components

74LS378N	74LS40N	74LS51D	74LS74N
74LS378N	74LS40N	74LS51N	74LS74N
74LS379D	74LS42D	74LS51N	74LS75D
74LS379D	74LS42D	74LS540DW	74LS75D
74LS379N	74LS42N	74LS540N	74LS75N
74LS379N	74LS42N	74LS541DW	74LS75N
74LS37D	74LS445D	74LS541N	74LS76D
74LS37D	74LS445D	74LS54D	74LS76D
74LS37N	74LS445N	74LS54D	74LS76N
74LS38D	74LS445N	74LS54N	74LS76N
74LS38D	74LS465DW	74LS54N	74LS77W
74LS38N	74LS465DW	74LS55D	74LS77W
74LS38N	74LS465N	74LS55D	74LS78D
74LS393D	74LS465N	74LS55N	74LS78D
74LS393D	74LS466DW	74LS55N	74LS78N
74LS393N	74LS466DW	74LS69D	74LS78N
74LS393N	74LS466N	74LS69D	74LS86D
74LS395D	74LS466N	74LS69N	74LS86D
74LS395D	74LS47D	74LS69N	74LS86N
74LS395N	74LS47D	74LS73D	74LS86N
74LS395N	74LS47N	74LS73D	74LS90D
74LS399D	74LS47N	74LS73N	74LS90D
74LS399N	74LS48D	74LS73N	74LS90N
74LS40D	74LS48N	74LS74D	74LS90N
74LS40D	74LS51D	74LS74D	74LS91D

Multisim 14.0 Base Components

74LS91D	75 mF [C0805C759KBGAC TU]	75 pF [C2225C750KBGAC TU]	750 pF [C2220C751KBGAC TU]
74LS91N			
74LS91N	75 pF [C0603C750K5GACT U]	750 pF [C0402C751K1HACT U]	750 pF [C2225C751KBGAC TU]
74LS92D			
74LS92D	75 pF [C0805C750K2GACT U]	750 pF [C0402C751K3HACT U]	777778-01
74LS92N			777779-01
74LS92N			779157-01
74LS93D	75 pF [C0805C750KBGAC TU]	750 pF [C0402C751K5HACT U]	781334-01
74LS93D			7Line_Bussed
74LS93N	75 pF [C0805C750KCGAC TU]	750 pF [C0603C751K1HACT U]	7Line_Isolated
74LS93N			7POS_ROTARY
74STD06N	75 pF [C1206C750K5GACT U]	750 pF [C0603C751K3HACT U]	8.2 nF [C0402C822K3RACT U]
74STD07N			
74STD116N	75 pF [C1206C750KBGAC TU]	750 pF [C0603C751K5GACT U]	8.2 nF [C0402C822K4RACT U]
74STD150N			
74STD154N	75 pF [C1210C750KBGAC TU]	750 pF [C0603C751K5HACT U]	8.2 nF [C0402C822K5RACT U]
74STD159N			
74STD16N	75 pF [C1812C750KBGAC TU]	750 pF [C1210C751KBGAC TU]	8.2 nF [C0402C822K9RACT U]
74STD17N			
74STD198N	75 pF [C1825C750KBGAC TU]	750 pF [C1812C751KBGAC TU]	8.2 nF [C0603C822K1RACT U]
74STD199N			
74STD25N	75 pF [C2220C750KBGAC TU]	750 pF [C1825C751KBGAC TU]	8.2 nF [C0603C822K3GACT U]
74STD39N			
74STD45N			
74STD72N			

Multisim 14.0 Base Components

8.2 nF [C0603C822K3HACT U]	8.2 nF [C0805C822K4RACT U]	8.2 nF [C1210C822K5GACT U]	8.2 uF [C1210C825K3PACT U]
8.2 nF [C0603C822K3RACT U]	8.2 nF [C0805C822K5GACT U]	8.2 nF [C1210C822K5RACT U]	8.2 uF [C1210C825K4PACT U]
8.2 nF [C0603C822K4RACT U]	8.2 nF [C0805C822K5HACT U]	8.2 nF [C1210C822KARACT U]	80C186EA13 80C186EA20 80C186EA25
8.2 nF [C0603C822K5RACT U]	8.2 nF [C0805C822K5RACT U]	8.2 nF [C1812C822K5GACT U]	80C186EB13 80C186EB20
8.2 nF [C0805C822K1GACT U]	8.2 nF [C1206C822K1HACT U]	8.2 nF [C1812C822K5RACT U]	80C186EB25 80C188EA13
8.2 nF [C0805C822K1HACT U]	8.2 nF [C1206C822K1RACT U]	8.2 nF [C2220C822K2GACT U]	80C188EA20 80C188EA25
8.2 nF [C0805C822K1RACT U]	8.2 nF [C1206C822K2RACT U]	8.2 uF [A700V825M016AT E045]	80C188EB13 80C188EB20
8.2 nF [C0805C822K2RACT U]	8.2 nF [C1206C822K3HACT U]	8.2 uF [C1206C825K4PACT U]	80C188EB25 80L186EA13
8.2 nF [C0805C822K3GACT U]	8.2 nF [C1206C822K5HACT U]	8.2 uF [C1206C825K8PACT U]	80L186EB13 80L186EB16
8.2 nF [C0805C822K3HACT U]	8.2 nF [C1206C822K5RACT U]	8.2 uF [C1206C825K8RACT U]	80L188EA13 80L188EB13
8.2 nF [C0805C822K3RACT U]	8.2 nF [C1206C822KARACT U]	8.2 uF [C1206C825K9RACT U]	80L188EB16 80SQ045NG 80SQ045NRLG

Multisim 14.0 Base Components

82 mF [C0603C829K2GACT U]	82 nF [C0805C823K3RACT U]	82 nF [C1206C823K3RACT U]	82 nF [C1210C823K1RACT U]
82 mF [C0805C829K5GACT U]	82 nF [C0805C823K4RACT U]	82 nF [C1206C823K5HACT U]	82 nF [C1210C823K3HACT U]
82 mF [C0805C829KBGAC TU]	82 nF [C0805C823K5RACT U]	82 nF [C1206C823K5RACT U]	82 nF [C1210C823K5GACT U]
82 nF [C0402C823K4RACT U]	82 nF [C0805C823K8RACT U]	82 nF [C1206C823KARACT U]	82 nF [C1210C823K5HACT U]
82 nF [C0402C823K8RACT U]	82 nF [C0805C823M5UAC TU]	82 nF [C1206C823M5UAC TU]	82 nF [C1210C823K5RACT U]
82 nF [C0402C823K9RACT U]	82 nF [C0805F823K3RACT U]	82 nF [C1206F823K1RACT U]	82 nF [C1210C823KARACT U]
82 nF [C0603C823K3RACT U]	82 nF [C0805F823K4RACT U]	82 nF [C1206F823K3RACT U]	82 nF [C1210C823M1UAC TU]
82 nF [C0603C823K4RACT U]	82 nF [C0805F823K5RACT U]	82 nF [C1206F823K4RACT U]	82 nF [C1210F823K2RACT U]
82 nF [C0603C823K5RACT U]	82 nF [C1206C823K1RACT U]	82 nF [C1206F823K5RACT U]	82 nF [C1812C823K1GACT U]
82 nF [C0603C823K8RACT U]	82 nF [C1206C823K2RACT U]	82 nF [C1210C823K1GACT U]	82 nF [C1812C823K1HACT U]
82 nF [C0805C823K1RACT U]	82 nF [C1206C823K3HACT U]	82 nF [C1210C823K1HACT U]	82 nF [C1812C823K5GACT U]

Multisim 14.0 Base Components

82 nF [C1812C823K5HACT U]	82 pF [C0805C820K3GACT U]	82 pF [C2220C820KBGAC TU]	82 uF [A700V826M2R5AT E025]
82 nF [C1812C823K5RACT U]	82 pF [C0805C820K5GACT U]	82 pF [C2225C820KBGAC TU]	82 uF [A700V826M2R5AT E028]
82 nF [C2220C823K1GACT U]	82 pF [C0805C820KBGAC TU]	82 pF [CA064C820K2GAC TU]	82 uF [T520C826M008AT E025]
82 nF [C2220C823K2GACT U]	82 pF [C1206C820K1GACT U]	82 pF [CDR31BP820BKSM]	82 uF [T520C826M008AT E045]
82 nF [C2220C823K5GACT U]	82 pF [C1206C820K2GACT U]	82 uF [A700V826M004AT E018]	820 nF [C0603C824K8PACT U]
82 pF [C0201C820K3GACT U]	82 pF [C1206C820K5GACT U]	82 uF [A700V826M004AT E025]	820 nF [C0805C824K4RACT U]
82 pF [C0402C820K3GACT U]	82 pF [C1206C820KBGAC TU]	82 uF [A700V826M004AT E028]	820 nF [C0805C824K8RACT U]
82 pF [C0402C820K5GACT U]	82 pF [C1206C820KCGAC TU]	82 uF [A700V826M006AT E018]	820 nF [C1206C824K3RACT U]
82 pF [C0603C820K5GACT U]	82 pF [C1210C820KBGAC TU]	82 uF [A700V826M006AT E025]	820 nF [C1206C824K4RACT U]
82 pF [C0805C820K1GACT U]	82 pF [C1812C820KBGAC TU]	82 uF [A700V826M006AT E028]	820 nF [C1206F824K4RACT U]
82 pF [C0805C820K2GACT U]	82 pF [C1825C820KBGAC TU]	82 uF [A700V826M2R5AT E018]	820 nF [C1210C824K5RACT U]

Multisim 14.0 Base Components

820 nF [C1210C824K8RACT U]	820 nF [C2220C824KARACT U]	820 pF [C0603C821K1HACT U]	820 pF [C0805C821K2RACT U]
820 nF [C1210F824K3RACT U]	820 nF [C2225C824K5RACT U]	820 pF [C0603C821K1RACT U]	820 pF [C0805C821K4GACT U]
820 nF [C1210F824K4RACT U]	820 nF [C2225C824KARACT U]	820 pF [C0603C821K2RACT U]	820 pF [C0805C821K4RACT U]
820 nF [C1812C824K5RACT U]	820 pF [C0402C821K1HACT U]	820 pF [C0603C821K3GACT U]	820 pF [C0805C821K5GACT U]
820 nF [C1812C824M5UAC TU]	820 pF [C0402C821K3GACT U]	820 pF [C0603C821K3HACT U]	820 pF [C0805C821K5RACT U]
820 nF [C1812F824K1RACT U]	820 pF [C0402C821K3HACT U]	820 pF [C0603C821K3RACT U]	820 pF [C1206C821K1GACT U]
820 nF [C1812F824K3RACT U]	820 pF [C0402C821K3RACT U]	820 pF [C0603C821K4RACT U]	820 pF [C1206C821K2GACT U]
820 nF [C1812F824K5RACT U]	820 pF [C0402C821K4RACT U]	820 pF [C0603C821K5GACT U]	820 pF [C1206C821K5GACT U]
820 nF [C1825C824KARACT U]	820 pF [C0402C821K5HACT U]	820 pF [C0603C821K5HACT U]	820 pF [C1210C821KBGAC TU]
820 nF [C2220C824K1RACT U]	820 pF [C0402C821K5RACT U]	820 pF [C0603C821K5RACT U]	820 pF [C1812C821K2GACT U]
820 nF [C2220C824K5RACT U]	820 pF [C0402C821K8RACT U]	820 pF [C0805C821K1RACT U]	820 pF [C1812C821K5GACT U]

Multisim 14.0 Base Components

820 pF [C1812C821KBGAC TU]	9.1 nF [C0805C912K5GACT U]	91 pF [C1206C910KBGAC TU]	910 pF [C0603C911K5GACT U]
820 pF [C1825C821KBGAC TU]	9.1 nF [C0805C912K5HACT U]	91 pF [C1210C910KBGAC TU]	910 pF [C0603C911K5HACT U]
820 pF [C2220C821KBGAC TU]	9.1 nF [C1206C912K1HACT U]	91 pF [C1812C910KBGAC TU]	910 pF [C0805C911K5GACT U]
820 pF [C2225C821KBGAC TU]	9.1 nF [C1206C912K3GACT U]	91 pF [C1825C910KBGAC TU]	910 pF [C1210C911KBGAC TU]
820 pF [CDR32BP821BKSM]	9.1 nF [C1206C912K3HACT U]	91 pF [C2220C910KBGAC TU]	910 pF [C1812C911KBGAC TU]
8550-4500PL 87520-0010BLF	9.1 nF [C1206C912K5HACT U]	91 pF [C2225C910KBGAC TU]	910 pF [C1825C911KBGAC TU]
8Line_Bussed 8Line_Isolated	9.1 nF [CDR35BP912BKSM]	910 pF [C0402C911K1HACT U]	910 pF [C2220C911KBGAC TU]
8POS_ROTARY 9.1 nF [C0603C912K3HACT U]	91 mF [C0805C919KBGAC TU]	910 pF [C0402C911K3HACT U]	910 pF [C2225C911KBGAC TU]
9.1 nF [C0805C912K1GACT U]	91 pF [C0805C910K2GACT U]	910 pF [C0402C911K5HACT U]	9Line_Bussed 9Line_Isolated
9.1 nF [C0805C912K1HACT U]	91 pF [C0805C910KBGAC TU]	910 pF [C0603C911K1HACT U]	ABM_CURRENT ABM_VOLTAGE
9.1 nF [C0805C912K3HACT U]	91 pF [C1206C910K1GACT U]	910 pF [C0603C911K3HACT U]	AC_CURRENT AC_POWER AC_VOLTAGE

Multisim 14.0 Base Components

ACML-7400-000E	ACPL-217-50CE	ACPL-H342-060E	ACPL-M61T-000E
ACML-7410-000E	ACPL-217-50DE	ACPL-K342-000E	ACPL-M61T-060E
ACML-7420-000E	ACPL-217-560E	ACPL-K342-060E	ACPL-M71T-000E
ACNW261L-000E	ACPL-217-56AE	ACPL-K34T-000E	ACPL-M71T-060E
ACNW261L-300E	ACPL-217-56BE	ACPL-K34T-060E	ACPL-M72T-000E
ACPL-021L-000E	ACPL-217-56CE	ACPL-K43T-000E	ACPL-M72T-060E
ACPL-021L-060E	ACPL-217-56DE	ACPL-K43T-060E	ACPL-P340-000E
ACPL-024L-000E	ACPL-312U-000E	ACPL-K44T-000E	ACPL-P340-060E
ACPL-024L-060E	ACPL-312U-300E	ACPL-K44T-060E	ACPL-P341-000E
ACPL-054L-000E	ACPL-32JT-000E	ACPL-K54L-000E	ACPL-P341-060E
ACPL-054L-060E	ACPL-331J-000E	ACPL-K54L-060E	ACPL-P343-000E
ACPL-061L-000E	ACPL-332J-000E	ACPL-K64L-000E	ACPL-P343-060E
ACPL-061L-060E	ACPL-336J-000E	ACPL-K64L-060E	ACPL-P345-000E
ACPL-064L-000E	ACPL-337J-000E	ACPL-M21L-000E	ACPL-P345-060E
ACPL-064L-060E	ACPL-339J-000E	ACPL-M21L-060E	ACPL-P346-000E
ACPL-077L-000E	ACPL-34JT-000E	ACPL-M43T-000E	ACPL-P346-060E
ACPL-077L-060E	ACPL-782T-000E	ACPL-M43T-060E	ACPL-W340-000E
ACPL-0820-000E	ACPL-782T-300E	ACPL-M46T-000E	ACPL-W340-060E
ACPL-214-500E	ACPL-C61L-000E	ACPL-M46T-060E	ACPL-W341-000E
ACPL-214-50AE	ACPL-C61L-060E	ACPL-M49T-000E	ACPL-W341-060E
ACPL-214-560E	ACPL-C790-000E	ACPL-M49T-060E	ACPL-W343-000E
ACPL-214-56AE	ACPL-C79A-000E	ACPL-M50L-000E	ACPL-W343-060E
ACPL-217-500E	ACPL-C79B-000E	ACPL-M50L-060E	ACPL-W345-000E
ACPL-217-50AE	ACPL-C87AT-000E	ACPL-M61L-000E	ACPL-W345-060E
ACPL-217-50BE	ACPL-H342-000E	ACPL-M61L-060E	ACPL-W346-000E

Multisim 14.0 Base Components

ACPL-W346-060E	AD507KH	AD544KH	AD548SQ
ACPL-W50L-000E	AD507SH	AD544LH	AD548TH
ACPL-W50L-060E	AD509JH	AD544SH	AD548TQ
ACPL-W61L-000E	AD509KH	AD545AJH	AD549JH
ACPL-W61L-060E	AD509SH	AD545AKH	AD549KH
ACSL-6400-00TE	AD515AJH	AD545ALH	AD549LH
ACSL-6400-06TE	AD515AKH	AD545AMH	AD549SH
ACSL-7210-00RE	AD515ALH	AD546JN	AD549SH/883B
ACSL-7210-06RE	AD517JH	AD546KN	AD5530_SO16
ACTEL-FLASHPRO-HDR	AD517KH	AD547JH	AD5531_SO16
	AD517LH	AD547KH	AD5539JN
AD1580ART	AD517SH	AD547LH	AD5539JQ
AD1580ARTZ	AD5260_SO14	AD547SH	AD5539SQ
AD1580BKSZ	AD5262_SO16	AD548AH	AD5539SQ/883B
AD1580BRT	AD5280_SO14	AD548AQ	AD581JH
AD1580BRTZ	AD5282_SO16	AD548AR	AD581KH
AD22050N	AD536AJD	AD548BH	AD581LH
AD22050R	AD536AJH	AD548BQ	AD581SH
AD22057N	AD536AJQ	AD548BR	AD581TH
AD22057R	AD536ASE/883B	AD548CH	AD581UH
AD380JH	AD542JH	AD548CQ	AD584JH
AD380KH	AD542KH	AD548JN	AD584JN
AD380LH	AD542LH	AD548JR	AD584KH
AD380SH	AD542SH	AD548KN	AD584KN
AD507JH	AD544JH	AD548SH	AD584LH

Multisim 14.0 Base Components

AD584SH	AD602AR	AD626BN	AD636KH
AD584TH	AD602JN	AD627AN	AD637AQ
AD587JN	AD603AQ	AD627AR	AD637AR
AD587JNZ	AD603AR	AD627BN	AD637ARZ
AD587JQ	AD604AN	AD627BR	AD637BR
AD587JR	AD604AR	AD628ARMZ	AD637BRZ
AD587JRZ	AD604ARS	AD628ARZ	AD637JD
AD587KN	AD605AN	AD629AN	AD637JDZ
AD587KR	AD605AR	AD629AR	AD637JQ
AD587KRZ	AD620AN	AD629BN	AD637JRZ
AD587UQ	AD620AR	AD629BR	AD637JRZ-R7
AD588AD	AD620BN	AD630AD	AD637JRZ-RL
AD588AQ	AD620BR	AD630AR	AD637KDZ
AD588ARWZ	AD620SQ	AD630BD	AD637KQ
AD588BD	AD623AN	AD630JN	AD637KRZ
AD588BQ	AD623AR	AD630KN	AD637SD
AD588JQ	AD623ARM	AD630SD	AD637SD/883B
AD588KQ	AD623BN	AD630SE/883B	AD637SQ/883B
AD588SD	AD623BR	AD633AN	AD642JH
AD588TD	AD624AD	AD633AR	AD642KH
AD588TQ/883B	AD624BD	AD633JN	AD642LH
AD600AQ	AD624CD	AD633JR	AD642SH
AD600AR	AD624SD	AD636JD	AD644JH
AD600JN	AD626AN	AD636JH	AD644KH
AD602AQ	AD626AR	AD636KD	AD644LH

Multisim 14.0 Base Components

AD644SH	AD704TQ/883B	AD708BQ	AD712JN
AD645AH	AD705AQ	AD708JN	AD712JR
AD645BH	AD705BQ	AD708SH	AD712KN
AD645JN	AD705JN	AD708SH/883B	AD712KR
AD645KN	AD705JR	AD708SQ	AD712SH
AD645SH	AD705KN	AD711AH	AD712SQ
AD647JH	AD705TQ	AD711AQ	AD712SQ/883B
AD647KH	AD706AQ	AD711BH	AD712TH
AD647LH	AD706AR	AD711BQ	AD712TQ
AD647SE	AD706BQ	AD711CH	AD712TRZ-EP
AD647SEB	AD706JN	AD711CQ	AD713AQ
AD647SH	AD706JR	AD711JN	AD713BQ
AD680AN	AD706KN	AD711JR	AD713JN
AD680AR	AD706TQ	AD711KN	AD713JR
AD680JR	AD707AH	AD711KR	AD713JR-16
AD680JTZ	AD707AQ	AD711SH	AD713KN
AD704AN	AD707AR	AD711SQ	AD713SQ
AD704AQ	AD707JN	AD711TH	AD713SQ/883B
AD704AR	AD707KN	AD711TQ	AD713TQ
AD704BQ	AD707KR	AD712AH	AD713TQ/883B
AD704JN	AD707TH	AD712AQ	AD734AN
AD704JR	AD707TQ	AD712BH	AD734AQ
AD704JR-16	AD708AH	AD712BQ	AD734BN
AD704KN	AD708AQ	AD712CH	AD734BQ
AD704TQ	AD708BH	AD712CQ	AD734SQ

Multisim 14.0 Base Components

AD734SQ/883B	AD743SQ	AD745SQ/883B	AD8000YRDZ
AD736AQ	AD743SQ/883B	AD746AQ	AD8001AN
AD736AR	AD744AH	AD746BQ	AD8001AQ
AD736JNZ	AD744AQ	AD746JN	AD8001AR
AD737AN	AD744BH	AD746JR	AD8001ART
AD737AR	AD744BQ	AD746SQ	AD8002AN
AD737BQ	AD744CH	AD780AN	AD8002AR
AD741CH	AD744CQ	AD780AR	AD8002ARM
AD741CN	AD744JN	AD780BN	AD8003ACPZ
AD741H	AD744JR	AD780BR	AD8003ACPZ-R2
AD741JH	AD744KN	AD795BH	AD8004AN
AD741JN	AD744KR	AD795JN	AD8004AR
AD741KH	AD744SH	AD795JR	AD8004AR-14
AD741KN	AD744SQ	AD795JRZ	AD8004SQ
AD741LH	AD744TH	AD795KN	AD8005AN
AD741LN	AD744TH/883B	AD796AN	AD8005AR
AD741SH	AD744TQ	AD796AR	AD8005ART
AD743AN	AD745AN	AD796BN	AD8007AKS
AD743AQ	AD745AQ	AD796SQ/883B	AD8007AR
AD743AR	AD745AR	AD797AN	AD8008AR
AD743BQ	AD745BQ	AD797AR	AD8008ARM
AD743JN	AD745JN	AD797BN	AD8009AR
AD743JR	AD745JR	AD797SQ	AD8009ARZ
AD743KN	AD745KN	AD8000YCPZ	AD8009JRT
AD743KR	AD745SQ	AD8000YCPZ-REEL	AD8010AN

Multisim 14.0 Base Components

AD8010AR	AD8024AR	AD8031BRZ	AD8042AN
AD8010AR-16	AD8027AR	AD8032AN	AD8042AR
AD8011AN	AD8027ART	AD8032ANZ	AD8044AN
AD8011AR	AD8027ARTZ	AD8032AR	AD8044AR
AD8012AR	AD8027ARTZ-R2	AD8032ARM	AD8045ACP
AD8012ARM	AD8027ARTZ-REEL	AD8032ARMZ	AD8045ACPZ-R2
AD8012ARMZ	AD8027ARTZ-REEL7	AD8032ARZ	AD8045ARD
AD8014AR	AD8027ARZ	AD8032BN	AD8045ARDZ
AD8014ART	AD8027ARZ-REEL	AD8032BNZ	AD8047AN
AD8016ARB	AD8027ARZ-REEL7	AD8032BR	AD8047AR
AD8016ARE	AD8028ARMZ	AD8032BRZ	AD8048AN
AD8016AREZ	AD8028ARZ	AD8033AKS	AD8048AR
AD8016ARP	AD8029AKS	AD8033AR	AD8051AR
AD8017AR	AD8029AR	AD8034AR	AD8051ART
AD8018AR	AD8030AR	AD8034ART	AD8052AR
AD8018ARU	AD8030ARJ	AD8036AN	AD8052ARM
AD8021AR	AD8031AN	AD8036AR	AD8054AR
AD8021ARM	AD8031ANZ	AD8038AKS	AD8054ARU
AD8021ARMZ	AD8031AR	AD8038AR	AD8055AN
AD8021ARZ	AD8031ART	AD8039AR	AD8055AR
AD8022AR	AD8031ARTZ	AD8039ART	AD8055ART
AD8022ARM	AD8031ARZ	AD8040AR	AD8055ARZ
AD8022ARMZ	AD8031BN	AD8040ARU	AD8056AN
AD8022ARZ	AD8031BNZ	AD8041AN	AD8056AR
AD8023AR	AD8031BR	AD8041AR	AD8056ARM

Multisim 14.0 Base Components

AD8057AR	AD8092AR	AD8130AR	AD813AR
AD8057ART	AD8092ARM	AD8130ARM	AD813AR-14
AD8058AR	AD8099ACP	AD8131AR	AD8145YCPZ-R2
AD8058ARM	AD8099ACPZ-R2	AD8131ARM	AD8146ACPZ-R2
AD8061AR	AD8099ARD	AD8131ARMZ	AD8147ACPZ-R2
AD8061ART	AD8099ARDZ	AD8131ARZ	AD8148ACPZ-R2
AD8062AR	AD810AN	AD8132AR	AD815ARB-24
AD8062ARM	AD810AR	AD8132ARM	AD817AN
AD8062ARMZ	AD810SN	AD8132ARMZ	AD817AR
AD8062ARZ	AD810SR	AD8132ARZ	AD8184AN
AD8065AR	AD811AN	AD8133ACP-R2	AD818AN
AD8065ART	AD811AR-16	AD8137YCP	AD818AR
AD8065ARTZ	AD811AR-20	AD8137YCPZ	AD8205WHRZ
AD8065ARZ	AD811JR	AD8137YR	AD8205WHRZ-RL
AD8066AR	AD811SE/883B	AD8137YRZ	AD8205WYRZ
AD8066ARM	AD811SQ/883B	AD8138AR	AD8205WYRZ-R7
AD8066ARMZ	AD8129ARMZ	AD8138ARM	AD8205WYRZ-RL
AD8066ARZ	AD8129ARMZ-REEL	AD8138ARMZ	AD8205YRZ
AD8067ART	AD8129ARMZ-REEL7	AD8138ARZ	AD8205YRZ-R7
AD8072ARM	AD8129ARZ	AD8139ACP	AD8205YRZ-RL
AD8072JR	AD8129ARZ-REEL	AD8139ACPZ	AD8206WYRZ
AD8079AR	AD8129ARZ-REEL7	AD8139ACPZ-R2	AD8206WYRZ-R7
AD8079BR	AD812AN	AD8139ARD	AD8206WYRZ-RL
AD8091AR	AD812AR	AD8139ARDZ	AD8206YRZ
AD8091ART		AD813AN	AD8206YRZ-REEL

Multisim 14.0 Base Components

AD8206YRZ-REEL7	AD8218BRMZ	AD8224BCPZ-WP	AD822BR
AD8207WBRZ	AD8218BRMZ-R7	AD8224HACPZ-R7	AD822SQ
AD8207WBRZ-R7	AD8219BRMZ	AD8224HACPZ-RL	AD8235ACBZ-P7
AD8207WBRZ-RL	AD8219BRMZ-RL	AD8224HACPZ-WP	AD8236ARMZ
AD8208WBRMZ	AD8220ARMZ	AD8224HBCPZ-R7	AD8237ARMZ
AD8208WBRZ	AD8220ARMZ-R7	AD8224HBCPZ-RL	AD8237ARMZ-R7
AD8209WBRMZ	AD8220ARMZ-RL	AD8224HBCPZ-WP	AD8237ARMZ-RL
AD820AN	AD8220BRMZ	AD8225AR	AD823AN
AD820AR	AD8220BRMZ-R7	AD8226ARMZ	AD823AR
AD820BN	AD8220BRMZ-RL	AD8226ARZ	AD8244ARMZ
AD820BR	AD8220WARMZ	AD8226BRMZ	AD8244BRMZ
AD8210WYRZ	AD8220WARMZ-R7	AD8226BRZ	AD824AN
AD8210YRZ	AD8220WARMZ-RL	AD8227ARMZ	AD824AR-14
AD8211YRJZ-R2	AD8221AR	AD8227ARZ	AD824AR-16
AD8214ARMZ	AD8221ARM	AD8227BRMZ	AD824BN
AD8216WYRZ	AD8221BR	AD8227BRZ	AD8250ARMZ
AD8216WYRZ-R7	AD8222ACPZ-R7	AD8228ARMZ	AD8251ARMZ
AD8216WYRZ-RL	AD8222BCPZ-R7	AD8228ARZ	AD8253ARMZ
AD8216YRZ	AD8222HACPZ-R7	AD8228BRMZ	AD8253ARMZ-R7
AD8216YRZ-R7	AD8222HBCPZ-R7	AD8228BRZ	AD8253ARMZ-RL
AD8216YRZ-RL	AD8224ACPZ-R7	AD8229HDZ	AD825AR
AD8217BRMZ	AD8224ACPZ-RL	AD822AN	AD825AR-16
AD8217BRMZ-R7	AD8224ACPZ-WP	AD822AR	AD826AN
AD8217BRMZ-RL	AD8224BCPZ-R7	AD822ARM	AD826AR
AD8218BCPZ-RL	AD8224BCPZ-RL	AD822BN	AD8270ACPZ-R7

Multisim 14.0 Base Components

AD8273ARZ	AD827JR-16	AD8332ACPZ-R2	AD8397ARDZ
AD8273ARZ-R7	AD827SE/883B	AD8332ACPZ-R7	AD8397ARZ
AD8273ARZ-RL	AD827SQ	AD8332ACPZ-RL	AD840JN
AD8274ARMZ	AD827SQ/883B	AD8332ARU	AD840JQ
AD8274ARMZ-R7	AD828AN	AD8332ARU-REEL	AD840KN
AD8274ARMZ-RL	AD828AR	AD8332ARU-REEL7	AD840KQ
AD8274ARZ	AD829AQ	AD8332ARUZ	AD840SE-883B
AD8274ARZ-R7	AD829JN	AD8332ARUZ-R7	AD840SQ
AD8274ARZ-RL	AD829JR	AD8332ARUZ-RL	AD840SQ-883B
AD8275ARMZ	AD829SE/883B	AD8333ACPZ-REEL	AD8417BRMZ
AD8275BRMZ	AD829SQ	AD8333ACPZ-REEL7	AD8417WBRMZ
AD8276ARMZ	AD829SQ/883B	AD8333ACPZ-WP	AD8417WBRZ
AD8276ARZ	AD8304ARU	AD8334ACPZ	AD8417WHRMZ
AD8276BRMZ	AD830AN	AD8334ACPZ-REEL	AD8417WHRZ
AD8276BRZ	AD830JR	AD8334ACPZ-REEL7	AD8418ABRMZ
AD8277ARZ	AD8310ARM	AD8335ACPZ	AD8418AWBRMZ
AD8277BRZ	AD8330ACPZ-R2	AD8335ACPZ-REEL	AD8418AWBRZ
AD8278ARMZ	AD8330ACPZ-R7	AD8335ACPZ-REEL7	AD8418AWHRMZ
AD8278ARZ	AD8330ACPZ-RL	AD8336ACPZ-R7	AD8418AWHRZ
AD8278BRMZ	AD8330ARQZ	AD8336ACPZ-RL	AD8418BRMZ
AD8278BRZ	AD8330ARQZ-R7	AD8336ACPZ-WP	AD8418WBRMZ
AD8279ARZ	AD8330ARQZ-RL	AD8337BCPZ-R2	AD8418WBRZ
AD8279BRZ	AD8331ARQZ	AD8337BCPZ-REEL	AD841JH
AD827AQ	AD8331ARQZ-R7	AD8337BCPZ-REEL7	AD841JN
AD827JN	AD8331ARQZ-RL	AD8337BCPZ-WP	AD841JQ

Multisim 14.0 Base Components

AD841KH	AD8422ARMZ-R7	AD842KQ	AD843SH
AD841KN	AD8422ARMZ-RL	AD842SE	AD843SQ
AD841KQ	AD8422ARZ	AD842SH	AD843SQ/883B
AD841SE	AD8422ARZ-R7	AD842SQ	AD844AN
AD841SH	AD8422ARZ-RL	AD8436ACPZ-R7	AD844AQ
AD841SQ	AD8422BRMZ	AD8436ACPZ-RL	AD844BQ
AD8420ARMZ	AD8422BRMZ-R7	AD8436ACPZ-WP	AD844JRZ-16
AD8420ARMZ-R7	AD8422BRMZ-RL	AD8436ARQZ	AD844SQ
AD8420ARMZ-RL	AD8422BRZ	AD8436ARQZ-R7	AD8450ASTZ
AD8421ARMZ	AD8422BRZ-R7	AD8436ARQZ-RL	AD8451ASTZ
AD8421ARMZ-R7	AD8422BRZ-RL	AD8436BRQZ	AD845AQ
AD8421ARMZ-RL	AD8426ACPZ-R7	AD8436BRQZ-R7	AD845BQ
AD8421ARZ	AD8426ACPZ-WP	AD8436BRQZ-RL	AD845JN
AD8421ARZ-R7	AD8426BCPZ-R7	AD8436JCPZ-R7	AD845JR
AD8421ARZ-RL	AD8426BCPZ-WP	AD8436JCPZ-RL	AD845JR-16
AD8421BRMZ	AD8429ARZ	AD8436JCPZ-WP	AD845KN
AD8421BRMZ-R7	AD8429ARZ-R7	AD843AQ	AD845SQ
AD8421BRMZ-RL	AD8429BRZ	AD843BH	AD845SQ/883B
AD8421BRZ	AD8429BRZ-R7	AD843BQ	AD846AN
AD8421BRZ-R7	AD842JH	AD843JN	AD846AQ
AD8421BRZ-RL	AD842JN	AD843JR	AD846BQ
AD8421TRMZ-EP	AD842JQ	AD843JR-16	AD846SQ
AD8421TRMZ-EP-R7	AD842JR	AD843KN	AD8475ACPZ-R7
AD8422ARMZ	AD842KH	AD843SE	AD8475ACPZ-RL
	AD842KN	AD843SE/883B	AD8475ACPZ-WP

Multisim 14.0 Base Components

AD8475ARMZ	AD847JR	AD849JN	AD8519ART
AD8475ARMZ-R7	AD847SQ	AD849JR	AD8527AR
AD8475ARMZ-RL	AD847SQ/883B	AD849SQ	AD8529AR
AD8475BRMZ	AD848AQ	AD849SQ/883B	AD8529ARM
AD8475BRMZ-R7	AD848JN	AD8500AKSZ	AD8531AKS
AD8475BRMZ-RL	AD848JR	AD8502ARJZ	AD8531AR
AD8476ACPZ-R7	AD848SQ	AD8504ARUZ	AD8532AR
AD8476ACPZ-RL	AD848SQ/883B	AD8505ACBZ-R7	AD8532ARM
AD8476ACPZ-WP	AD8494ARMZ	AD8505ARJZ-RL	AD8532ARU
AD8476ARMZ	AD8494ARMZ-R7	AD8506ARMZ	AD8534AR
AD8476ARMZ-R7	AD8494CRMZ	AD8508ACBZ-REEL	AD8534ARU
AD8476ARMZ-RL	AD8494CRMZ-R7	AD8508ARUZ	AD8538ARZ
AD8476BCPZ-R7	AD8495ARMZ	AD8510AR	AD8538AUJZ
AD8476BCPZ-RL	AD8495ARMZ-R7	AD8510ARM	AD8538AUJZ-R2
AD8476BCPZ-WP	AD8495CRMZ	AD8510BR	AD8539ARMZ
AD8476BRMZ	AD8495CRMZ-R7	AD8512AR	AD8539ARZ
AD8476BRMZ-R7	AD8496ARMZ	AD8512ARM	AD8541AKS
AD8476BRMZ-RL	AD8496ARMZ-R7	AD8512BR	AD8541AR
AD8479ARZ	AD8496CRMZ	AD8513AR	AD8541ART
AD8479ARZ-RL	AD8496CRMZ-R7	AD8513ARU	AD8541ARZ
AD8479BRZ	AD8497ARMZ	AD8515AKS	AD8542AR
AD8479BRZ-RL	AD8497ARMZ-R7	AD8515ART	AD8542ARM
AD847AQ	AD8497CRMZ	AD8517ART	AD8542ARU
AD847AR	AD8497CRMZ-R7	AD8519AKS	AD8544AR
AD847JN	AD849AQ	AD8519AR	AD8544ARU

Multisim 14.0 Base Components

AD8546ARMZ	AD8594AR	AD8610AR	AD8622ARMZ
AD8548ARZ	AD8594ARU	AD8610ARM	AD8622ARZ
AD8548ARZ-R7	AD8597ACPZ-R2	AD8610ARZ	AD8624ACPZ-R2
AD8548ARZ-RL	AD8597ARZ	AD8610BR	AD8624ARUZ
AD8551AR	AD8599ARZ	AD8611AR	AD8625ARUZ
AD8551ARM	AD8601ART	AD8611ARM	AD8625ARZ
AD8552AR	AD8602AR	AD8612ARU	AD8626ARMZ
AD8552ARU	AD8602ARM	AD8613AKSZ	AD8626ARZ
AD8554AR	AD8603AUJZ	AD8613AUJZ	AD8627AKS
AD8554ARU	AD8604AR	AD8614ART	AD8627AKSZ
AD8561AN	AD8604ARQZ	AD8615AUJZ	AD8627AR
AD8561AR	AD8604ARUZ	AD8616AR	AD8627ARZ
AD8561ARU	AD8604DRU	AD8616ARM	AD8628AR
AD8564AN	AD8604DRZ	AD8617ACPZ-R2	AD8628ART
AD8564AR	AD8605ACB	AD8617ARMZ	AD8628AUJ
AD8565AKS	AD8605ART	AD8617ARZ	AD8629ARMZ
AD8565AKSZ	AD8606ACBZ-REEL	AD8617WARMZ-REEL	AD8629ARZ
AD8571AR	AD8606AR	AD8617WARZ-RL	AD8629WARZ-RL
AD8571ARM	AD8606ARM-REEL	AD8618AR	AD8630ARUZ
AD8572AR	AD8607AR	AD8618ARU	AD8630ARZ
AD8572ARU	AD8607ARM-REEL	AD8619ARUZ	AD8630WARZ-RL
AD8574AR	AD8608AR	AD8619ARZ	AD8631ART
AD8574ARU	AD8608ARU	AD8620AR	AD8631ARTZ
AD8591ART	AD8609AR	AD8620BR	AD8632AR
AD8592ARM	AD8609ARU		AD8632ARM

Multisim 14.0 Base Components

AD8632ARMZ	AD8651ARM	AD8671ARM	AD9610TH/883B
AD8632ARZ	AD8655ARMZ	AD8671ARMZ	AD9617AQ
AD8638ARJZ	AD8655ARZ	AD8672AR	AD9617BQ
AD8638ARZ	AD8656ARMZ	AD8672ARM	AD9617JN
AD8639ACPZ-R2	AD8656ARZ	AD8672ARMZ	AD9617JR
AD8639ARMZ	AD8657ACPZ-RL	AD8674AR	AD9617SQ
AD8639ARZ	AD8657ARMZ	AD8674ARU	AD9617TQ
AD8639WARZ	AD8659ACPZ-R7	AD8675ARMZ	AD9618AQ
AD8641AKSZ	AD8659ACPZ-RL	AD8675ARZ	AD9618BQ
AD8641AKSZ-R2	AD8659ARZ	AD8676ARMZ	AD9618JN
AD8641ARZ	AD8659ARZ-R7	AD8676ARZ	AD9618JR
AD8642ARMZ	AD8659ARZ-RL	AD8676BRMZ	AD9618SQ
AD8642ARZ	AD8661ACPZ-R2	AD8676BRZ	AD9618TQ
AD8643ACPZ-R2	AD8661ARZ	AD8677ARZ	AD9620AD
AD8643ARZ	AD8662ARMZ	AD8677AUJZ-R2	AD9620SD
AD8644AR	AD8662ARZ	AD8691AKSZ	AD9621AN
AD8644ARU	AD8663ACPZ	AD8691AUJZ	AD9622AN
AD8646ARMZ	AD8663ARZ	AD8692ARMZ	AD9623AN
AD8646ARZ	AD8664ARUZ	AD8692ARZ	AD9624AN
AD8646WARMZ-RL	AD8664ARZ	AD8694ARUZ	AD9630AN
AD8646WARZ-RL	AD8667ARMZ	AD8694ARZ	AD9630AQ
AD8648ARUZ	AD8667ARZ	AD8698AR	AD9630AR
AD8648ARZ	AD8669ARUZ	AD8698ARM	AD9631AN
AD8648WARUZ	AD8669ARZ	AD9218_FP48	AD9631AR
AD8651AR	AD8671AR	AD9610TH	AD9632AN

Multisim 14.0 Base Components

AD9632AR	ADA4004-2ARZ-RL	ADA4077-2ARMZ-RL	ADA4096-2WARMZ-R7
AD9841A-LQFP(48)	ADA4004-4ACPZ-R2	ADA4077-2ARZ	ADA4096-2WARMZ-RL
AD9842A-LQFP(48)	ADA4004-4ACPZ-R7	ADA4077-2ARZ-R7	ADA4096-4ACPZ-R7
ADA4000-1ARZ	ADA4004-4ACPZ-RL	ADA4077-2ARZ-RL	ADA4096-4ARUZ
ADA4000-1AUJZ	ADA4004-4ARZ	ADA4077-2BRZ	ADA4500-2ACPZ-R7
ADA4000-1AUJZ-RL	ADA4004-4ARZ-R7	ADA4077-2BRZ-R7	ADA4500-2ACPZ-RL
ADA4000-2ARMZ	ADA4004-4ARZ-RL	ADA4077-2BRZ-RL	ADA4500-2ARMZ
ADA4000-2ARZ	ADA4051-1AKSZ-R2	ADA4077-4ARUZ	ADA4500-2ARMZ-R7
ADA4000-4ARUZ	ADA4051-1ARJZ-R2	ADA4077-4ARZ	ADA4500-2ARMZ-RL
ADA4000-4ARZ	ADA4051-2ACPZ-R2	ADA4084-2ARMZ	ADA4505-1ACBZ-R7
ADA4001-2ARZ	ADA4051-2ARMZ	ADA4084-2ARMZ-R7	ADA4505-1ARJZ-R2
ADA4001-2ARZ-R7	ADA4062-2ACPZ-RL	ADA4084-2ARMZ-RL	ADA4505-2ACBZ-RL
ADA4001-2ARZ-RL	ADA4062-2ARMZ	ADA4084-2ARZ	ADA4505-2ARMZ
ADA4004-1ARJZ-R2	ADA4062-2ARZ	ADA4084-2ARZ-R7	ADA4505-4ACBZ-RL
ADA4004-1ARJZ-R7	ADA4062-2BRZ	ADA4084-2ARZ-RL	ADA4505-4ARUZ
ADA4004-1ARJZ-RL	ADA4062-4ACPZ-R2	ADA4091-2ACPZ-R2	ADA4528-1ARMZ
ADA4004-1ARZ	ADA4062-4ARUZ	ADA4091-2ARZ	ADA4610-2ACPZ-R7
ADA4004-1ARZ-R7	ADA4075-2ACPZ-RL	ADA4091-4ACPZ-R2	ADA4610-2ACPZ-RL
ADA4004-1ARZ-RL	ADA4075-2ARZ	ADA4091-4ARUZ	ADA4610-2ARMZ
ADA4004-2ARMZ	ADA4077-1ARMZ	ADA4092-4ARUZ	ADA4610-2ARMZ-R7
ADA4004-2ARMZ-R7	ADA4077-1ARZ	ADA4096-2ACPZ-R7	ADA4610-2ARMZ-RL
ADA4004-2ARMZ-RL	ADA4077-1BRZ	ADA4096-2ARMZ	
ADA4004-2ARMZ	ADA4077-2ARMZ		
ADA4004-2ARZ	ADA4077-2ARMZ-R7		
ADA4004-2ARZ-R7			

Multisim 14.0 Base Components

ADA4610-2ARZ	ADA4666-2ACPZ-R7	ADA4850-1YCPZ	ADA4860-1YRJZ-R2
ADA4610-2ARZ-R7	ADA4666-2ACPZ-RL	ADA4850-1YCPZ-R2	ADA4860-1YRJZ-RL
ADA4610-2ARZ-RL	ADA4666-2ARMZ	ADA4850-2YCPZ-R2	ADA4860-1YRJZ-RL7
ADA4610-2BRZ	ADA4666-2ARMZ-R7	ADA4850-2YCPZ-RL	ADA4861-3YRZ
ADA4610-2BRZ-R7	ADA4666-2ARMZ-RL	ADA4851-1WYRJZ-R7	ADA4861-3YRZ-RL
ADA4610-2BRZ-RL		ADA4851-1YRJZ-R2	ADA4861-3YRZ-RL7
ADA4627-1ACPZ-RL	ADA4691-2ACBZ-R7	ADA4851-1YRJZ-RL	ADA4870ARRZ
ADA4627-1ARZ	ADA4691-2ACPZ-R7	ADA4851-2WYRMZ	ADA4891-1ARJZ-R7
ADA4627-1BRZ	ADA4691-4ACPZ-R7	ADA4851-2YRMZ	ADA4891-1ARZ
ADA4637-1ACPZ-R2	ADA4692-2ACPZ-R7	ADA4851-2YRMZ-RL	ADA4891-2ARMZ
ADA4637-1ARZ	ADA4692-2ARZ		ADA4891-2ARZ
ADA4637-1BRZ	ADA4692-4ARUZ	ADA4851-4WYRUZ	ADA4891-3ARUZ
ADA4638-1ACPZ-R7	ADA4700-1ARDZ	ADA4851-4YRUZ	ADA4891-3ARZ
ADA4638-1ACPZ-RL	ADA4805-1AKSZ-R2	ADA4851-4YRUZ-RL	ADA4891-4ARUZ
ADA4638-1ARZ	ADA4805-1ARJZ-R2	ADA4853-1AKSZ-R2	ADA4891-4ARZ
ADA4638-1ARZ-R7	ADA4817-1ACPZ-R2	ADA4853-2YCPZ-R2	ADA4895-2ARMZ
ADA4638-1ARZ-RL	ADA4817-1ACPZ-R7	ADA4853-3WYCPZ-R7	ADA4895-2ARMZ-R7
ADA4661-2ACPZ-R7	ADA4817-1ACPZ-RL	ADA4853-3YCPZ-R2	ADA4895-2ARMZ-RL
ADA4661-2ACPZ-RL	ADA4817-1ARDZ	ADA4853-3YRUZ	
ADA4661-2ARMZ	ADA4817-1ARDZ-R7	ADA4855-3YCPZ-R2	ADA4896-2ACPZ-R2
ADA4661-2ARMZ-R7	ADA4817-1ARDZ-RL	ADA4857-1YCPZ-R2	ADA4896-2ACPZ-R7
ADA4661-2ARMZ-RL	ADA4817-2ACPZ-R2	ADA4857-1YRZ	ADA4896-2ACPZ-RL
	ADA4817-2ACPZ-R7	ADA4857-2YCPZ-R2	ADA4896-2ARMZ
ADA4665-2ARMZ	ADA4817-2ACPZ-RL		
ADA4665-2ARZ	ADA4841-1YRZ	ADA4858-3ACPZ-R2	

Multisim 14.0 Base Components

ADA4896-2ARMZ-R7	ADA4938-1ACPZ-R2	ADG1213YCPZ-500RL7	ADG411BN
	ADA4938-2ACPZ-R2		ADG411BR
ADA4896-2ARMZ-RL	ADA4939-1YCPZ-R2	ADG1213YRUZ	ADG411BRU
ADA4897-1ARJZ-R2	ADA4939-2YCPZ-R2	ADG1236YCPZ-500RL7	ADG411TQ
ADA4897-1ARZ	ADA4940-1ACPZ-R2	ADG1236YRUZ	ADG412
ADA4897-1SRJZ-EPR7	ADA4940-1ACPZ-R7	ADG1311YRUZ	ADG412BN
	ADA4940-1ACPZ-RL	ADG1311YRZ	ADG412BR
ADA4897-2ARMZ	ADA4940-2ACPZ-R2	ADG1312YRUZ	ADG412BRU
ADA4897-2TRMZ-EP	ADA4940-2ACPZ-R7	ADG1312YRZ	ADG412TQ
	ADA4940-2ACPZ-RL	ADG1313YRUZ	ADG413BN
ADA4898-1YRDZ	ADA4941-1YCPZ-RL	ADG1313YRZ	ADG413BNZ
ADA4898-2YRDZ	ADA4941-1YRZ	ADG406BN	ADG413BR
ADA4899-1YCPZ	ADA4950-1YCPZ-R2	ADG406BP	ADG413BRUZ
ADA4899-1YCPZ-R2	ADA4950-2YCPZ-R2	ADG407BN	ADG426BN
ADA4899-1YRDZ	ADA4960-1ACPZ-R2	ADG407BP	ADG426BRS
ADA4922-1ACPZ-R2	ADC	ADG408	ADG441ABN
ADA4922-1ARDZ	ADC16	ADG408BN	ADG441ABR
ADA4927-1YCPZ-R2	ADD_FULL	ADG408BR	ADG441BN
ADA4927-2YCPZ	ADD_FULL4_FCR	ADG408BRU	ADG441BR
ADA4930-1YCPZ-R2	ADD_HALF	ADG408TQ	ADG441TQ
ADA4930-2YCPZ-R2	ADG1211YCPZ-500RL7	ADG409BN	ADG442BN
ADA4932-1YCPZ-R2	ADG1211YRUZ	ADG409BR	ADG444
ADA4932-2YCPZ-R2		ADG409BRU	ADG444ABN
ADA4937-1YCPZ-R2	ADG1212YCPZ-500RL7	ADG409TQ	ADG444ABR
ADA4937-2YCPZ-R2	ADG1212YRUZ	ADG411	ADG444BN

Multisim 14.0 Base Components

ADG444BR	ADG528FTQ	ADG659YCPZ	ADG741BKSZ-REEL
ADG508FBN	ADG601BRMZ	ADG659YRQ	ADG742BKSZ5-REEL
ADG508FBNZ	ADG601BRTZ-REEL	ADG659YRU	ADG742BKSZ-R2
ADG508FBRN	ADG602BRM	ADG663BRU	ADG749BKSZ-REEL
ADG508FBRUZ	ADG602BRTZ-REEL	ADG701BRJ-500RL7	ADG779BKSZ-R2
ADG508FBRW	ADG604YRU	ADG701BRM	ADG781BCP
ADG508FTQ	ADG604YRUZ	ADG701BRTZ-REEL	ADG782BCP
ADG509FBN	ADG608BN	ADG702BRJ-REEL7	ADG783BCP
ADG509FBRN	ADG608BR	ADG702BRM	ADG787BCBZ-REEL
ADG509FBRUZ	ADG608BRU	ADG702BRTZ-REEL	ADG787BCPZ-REEL
ADG509FBRW	ADG608TRU	ADG711BR	ADG787BRMZ
ADG509FBRWZ	ADG609BN	ADG711BRU	ADG801BRM
ADG509FTQ	ADG609BR	ADG712BR	ADG801BRT-500RL7
ADG511BN	ADG609BRU	ADG712BRU	ADG802BCBZ-REEL7
ADG511BR	ADG609BRUZ	ADG713BR	ADG802BRM
ADG511TQ	ADG609BRZ	ADG713BRU	ADG802BRT-500RL7
ADG512BN	ADG611YRUZ	ADG719BRM	ADG811YCPZ-REEL
ADG512BR	ADG611YRZ	ADG719BRT-REEL	ADG811YRU
ADG512TQ	ADG612WYRUZ-REEL	ADG721ACPZ-REEL	ADG812YRU
ADG513BN	ADG612YRUZ	ADG721BRM	ADG813YRU
ADG513BR	ADG613YRUZ	ADG722ACPZ-REEL	ADG819BCB
ADG513TQ	ADG658YCPZ	ADG722BRM	ADG819BRM
ADG528F	ADG658YRQ	ADG723ACPZ-REEL	ADG819BRT
ADG528FBN	ADG658YRU	ADG723BRM	
ADG528FBP		ADG741BKSZ5-REEL	

Multisim 14.0 Base Components

ADG820BRM	ADS8364Y	ADSP-2161-TQFP(80)	ADTL084JRZ
ADG820BRT	ADSP-2101-PGA(68)		ADZS-BRKOUT-EX3
ADG821BRM	ADSP-2101-PLCC(68)	ADSP-2162-PLCC(68)	AIR_NC
ADG822BRM		ADSP-2162-PQFP(80)	AIR_NO
ADG823BRM	ADSP-2101-PQFP(80)		ALPHA_NUMERIC_COM_A_BLUE
ADG839YKSZ-500RL7	ADSP-2101-TQFP(80)	ADSP-2162-TQFP(80)	ALPHA_NUMERIC_COM_A_GREEN
ADG841YKSZ-500RL7	ADSP-2103-PLCC(68)	ADSP-2163-PLCC(68)	ALPHA_NUMERIC_COM_A_ORANGE
ADG842YKSZ-500RL7	ADSP-2103-PQFP(80)	ADSP-2163-PQFP(80)	ALPHA_NUMERIC_COM_A_RED
ADG849YKSZ-500RL7	ADSP-2103-TQFP(80)	ADSP-2163-TQFP(80)	ALPHA_NUMERIC_COM_A_YELLOW
ADG859BRYZ-REEL	ADSP-2105-PLCC(68)	ADSP-2164-PLCC(68)	ALPHA_NUMERIC_COM_K_BLUE
ADG859YRYZ-REEL		ADSP-2164-PQFP(80)	ALPHA_NUMERIC_COM_K_GREEN
ADG884BCBZ-REEL	ADSP-2111-PGA(100)	ADSP-2164-TQFP(80)	ALPHA_NUMERIC_COM_K_ORANGE
ADG884BCPZ-REEL	ADSP-2111-PQFP(100)		ALPHA_NUMERIC_COM_K_RED
ADG884BRMZ		ADSP-2191M-LQFP(144)	
ADR3425ARJZ-R2	ADSP-2115-PLCC(68)	ADTL082ARMZ	
ADR3425ARJZ-R7		ADTL082ARZ	ALPHA_NUMERIC_COM_K_YELLOW
ADR5040AKSZ-R2	ADSP-2115-PQFP(80)		
ADR5040ARTZ-R2	ADSP-2115-TQFP(80)	ADTL082JR	ALTERA-BYTEBLASTER-HDR
ADR5040BKSZ-R2		ADTL082JRZ	
ADR5040BRTZ-R2	ADSP-2161-PLCC(68)	ADTL084ARUZ	ALU_4BIT
ADS8320EB	ADSP-2161-PQFP(80)	ADTL084ARZ	AM_VOLTAGE
ADS8322YB		ADTL084JR	AM29520ADC

Multisim 14.0 Base Components

AM29520ADCB	AMP04EP	ARM-14-HDR	BA159-E3/54
AM29520AJC	AMP04ES	ARM-20-HDR	BA159GP
AM29520ALC	AMP04FP	ASP-134488-01	BA220
AM29520APC	AMP04FS	ASP-134603-01	BA221
AM29520APCB	ANALOG_SWITCH_	ASP-134604-01	BA223
AM29521ADC	VIRTUAL	ASP-134606-01	BA281
AM29521ADCB	AND_OR_I	ASSR-V621-002E	BA314
AM29521AJC	AND2	ASSR-V621-302E	BA315
AM29521ALC	AND2	ASSR-V622-002E	BA316
AM29521APC	AND3	ASSR-V622-302E	BA317
AM29521APCB	AND3	ATF750C-10PC	BA318
AM29LV800BB-70EI	AND4	ATF750C-10XC	BA423
AMMETER_H	AND4	ATF750C-15PC	BA423L
AMMETER_HR	AND5	ATF750C-15XC	BA481
AMMETER_V	AND5	ATF750CL-15PC	BA482
AMMETER_VR	AND6	ATF750CL-15XC	BA483
AMP01AX	AND6	ATP207-TL-H	BA484
AMP01BX	AND7	ATP301-TL-H	BA592
AMP01EX	AND7	ATP405-TL-H	BA595
AMP01FX	AND8	ATV2500BL-20JI	BA682
AMP01GS	AND8	ATV2500BQ-20JC	BA683
AMP02AZ	ANTI_PLUG	AVR-JTAG-HDR	BA885
AMP02EP	ARBITRARY_LAPLAC	B6S-E3/80	BA892
AMP02FP	E_FUNCTION	BA157GP	BA895
AMP02FS	ARBITRARY_SPICE_	BA158GP	BAL74
	BLOCK		

Multisim 14.0 Base Components

BAL99	BAR50-02L	BAS101	BAS16W
BAR_LED_BLUE	BAR50-02V	BAS101S	BAS17
BAR_LED_BLUE_FOUR	BAR61	BAS11	BAS170W
BAR_LED_BLUE_TEN	BAR63-02L	BAS116	BAS19
BAR_LED_GREEN	BAR63-02V	BAS116H	BAS20
BAR_LED_GREEN_FOUR	BAR63-02W	BAS116LT1G	BAS20LT1G
BAR_LED_GREEN_TEN	BAR63-03W	BAS116T	BAS21
BAR_LED_ORANGE	BAR63-04	BAS116TT1G	BAS21AVD
BAR_LED_ORANGE_FOUR	BAR63-04W	BAS125-04W	BAS21AW
BAR_LED_ORANGE_TEN	BAR63-05	BAS125-05W	BAS21H
BAR_LED_ORANGE_FOUR	BAR63-05W	BAS125-07W	BAS21HT1G
BAR_LED_ORANGE_TEN	BAR63-06	BAS140W	BAS21J
BAR_LED_RED	BAR63-06W	BAS15	BAS21M3T5G
BAR_LED_RED_FOUR	BAR64-02V	BAS16	BAS21SLT1G
BAR_LED_RED_TEN	BAR64-03W	BAS16-02L	BAS21SW
BAR_LED_YELLOW	BAR64-04	BAS16DXV6T1G	BAS21TMR6T1G
BAR_LED_YELLOW_FOUR	BAR64-04W	BAS16H	BAS21U
BAR_LED_YELLOW_TEN	BAR64-05W	BAS16J	BAS21VD
BAR_LED_YELLOW_FOUR	BAR64-06W	BAS16L	BAS21W
BAR_LED_YELLOW_TEN	BAR65-03W	BAS16LD	BAS28
BAR14-1	BAR67-02V	BAS16M3T5G	BAS29
BAR15-1	BAR74	BAS16P2T5G	BAS3010B-03W
BAR16-1	BAR81W	BAS16T	BAS3020B
	BAR88-02V	BAS16VV	BAS31
	BAR99	BAS16VY	BAS316

Multisim 14.0 Base Components

BAS32	BAS521	BAS86	BAT54
BAS321	BAS56	BAT120A	BAT54A
BAS32L	BAS70	BAT120C	BAT54AW
BAS35	BAS70-02L	BAT120S	BAT54C
BAS40	BAS70-02W	BAT15-02LRH	BAT54CLT1
BAS40-02L	BAS70-04	BAT15-03W	BAT54CLT1G
BAS40-04	BAS70-04LT1G	BAT15-05W	BAT54CLT3G
BAS40-05	BAS70-04W	BAT15-099	BAT54CM
BAS40-05V	BAS70-05	BAT160A	BAT54CV
BAS40-05W	BAS70-05W	BAT160C	BAT54CW
BAS40-06	BAS70-06	BAT160S	BAT54H
BAS40-06W	BAS70-06W	BAT165	BAT54J
BAS40-07	BAS70-07	BAT17	BAT54L
BAS40-07V	BAS70-07S	BAT17-04	BAT54M3T5G
BAS40-07W	BAS70-07V	BAT17-05	BAT54S
BAS40H	BAS70H	BAT17-05W	BAT54SW
BAS40L	BAS70L	BAT17-06W	BAT54T
BAS40W	BAS70VV	BAT17-07	BAT54VV
BAS40XY	BAS70W	BAT18	BAT54W
BAS416	BAS70XY	BAT18-04	BAT54WT1G
BAS45	BAS716	BAT18-05	BAT54XY
BAS45A	BAS81	BAT24-02LS	BAT60A
BAS45AL	BAS82	BAT240A	BAT60B
BAS45L	BAS83	BAT46WH	BAT62
BAS516	BAS85	BAT46WJ	BAT62-02L

Multisim 14.0 Base Components

BAT62-02W	BAT754	BAV199	BAV99LT1
BAT62-03W	BAT754A	BAV199W	BAV99LT1G
BAT62-07W	BAT754C	BAV20	BAV99LT3
BAT63-07W	BAT754L	BAV21	BAV99LT3G
BAT64	BAT754S	BAV23	BAV99S
BAT64-02W	BAT760	BAV23A	BAV99W
BAT64-04	BAT81	BAV23C	BAW101
BAT64-04W	BAT82	BAV23S	BAW101S
BAT64-05	BAT83	BAV45	BAW156
BAT64-05W	BAT85	BAV70	BAW56
BAT64-06	BAT854AW	BAV70DXV6T5G	BAW56LT1
BAT64-06W	BAT854CW	BAV70LT1	BAW56LT1G
BAT68	BAT854SW	BAV70LT1G	BAW56LT3G
BAT68-04	BAT854W	BAV70LT3G	BAW56M
BAT68-04W	BAT86	BAV70M	BAW56M3T5G
BAT68-06	BAT960	BAV70M3T5G	BAW56S
BAT68-06W	BAV10	BAV70S	BAW56T
BAT720	BAV100	BAV70T	BAW56TT1G
BAT721	BAV101	BAV70TT1G	BAW56W
BAT721A	BAV102	BAV70W	BAW62
BAT721C	BAV103	BAV74	BAX12
BAT721S	BAV105	BAV74LT1	BAX14
BAT74	BAV170	BAV74LT1G	BAX18
BAT74S	BAV18	BAV756S	BAY80
BAT74V	BAV19	BAV99	BB112

Multisim 14.0 Base Components

BB119	BB644	BBY51-03W	BC108BP
BB130	BB659	BBY52-02L	BC109BP
BB204B	BB659C	BBY52-02W	BC177AP
BB204G	BB659C-02V	BBY53-02L	BC178AP
BB212	BB664	BBY53-02V	BC182BP
BB215	BB664-02V	BBY53-02W	BC183BP
BB219	BB689	BBY53-03W	BC184BP
BB240	BB689-02V	BBY53-05W	BC212AP
BB241	BB804	BBY55-02V	BC213AP
BB249	BB809	BBY55-03W	BC237BP
BB405B	BB811	BBY56-02W	BC238BP
BB417	BB814	BBY56-03W	BC239BP
BB439	BB833	BBY57-02V	BC264A
BB515	BB837	BBY57-02W	BC264B
BB535	BB857	BBY57-05W	BC264C
BB545	BB909A	BBY58-02V	BC264D
BB555	BB909B	BBY58-02W	BC307AP
BB555-02V	BB910	BBY58-03W	BC308AP
BB565	BB911	BBY58-05W	BC337AP
BB565-02V	BB914	BBY58-06W	BC338AP
BB619	BBY31	BBY62	BC413BP
BB620	BBY39	BBY65-02V	BC414BP
BB639	BBY40	BBY66-02V	BC415AP
BB639C	BBY42	BBY66-05W	BC416AP
BB640	BBY51-02W	BC107BP	BC51-10PA

Multisim 14.0 Base Components

BC51-16PA	BC557BZL1G	BC807-40LT3G	BC846AT
BC51PA	BC558AP	BC807-40QA	BC846AW
BC52-10PA	BC559AP	BC807-40W	BC846B
BC52-16PA	BC55PA	BC807DS	BC846BDW1T1G
BC52PA	BC560AP	BC807W	BC846BLT1G
BC53-10PA	BC56-10PA	BC808-16	BC846BLT3G
BC53-16PA	BC56-16PA	BC817	BC846BMB
BC53PA	BC56PA	BC817-16	BC846BPDW1T1G
BC54-10PA	BC68-25PA	BC817-16W	BC846BPN
BC54-16PA	BC68PA	BC817-25	BC846BS
BC546BP	BC69-16PA	BC817-25LT1	BC846BT
BC547BG	BC69-25PA	BC817-25LT1G	BC846BW
BC547BP	BC69PA	BC817-25LT3G	BC846DS
BC547BRL1G	BC807	BC817-25QA	BC846S
BC547BZL1G	BC807-16	BC817-25W	BC846T
BC548BP	BC807-16LT1G	BC817-40	BC846W
BC549BP	BC807-16LT3G	BC817-40QA	BC847
BC54PA	BC807-16W	BC817-40W	BC847A
BC550BP	BC807-25	BC817DPN	BC847AM
BC55-10PA	BC807-25LT1G	BC817DS	BC847AMB
BC55-16PA	BC807-25LT3G	BC817W	BC847AT
BC556AP	BC807-25QA	BC846	BC847AW
BC557AP	BC807-25W	BC846A	BC847B
BC557BG	BC807-40	BC846ALT1G	BC847BDW1T1G
BC557BRL1G	BC807-40LT1G	BC846ALT3G	BC847BDW1T3

Multisim 14.0 Base Components

BC847BDW1T3G	BC848W	BC857A	BC859BW
BC847BM	BC849B	BC857AM	BC859C
BC847BMB	BC849BW	BC857AMB	BC859CW
BC847BPDW1T1	BC849C	BC857AT	BC860A
BC847BPDW1T1G	BC849CW	BC857AW	BC860B
BC847BPDW1T2G	BC850B	BC857B	BC860BW
BC847BPDW1T3G	BC850BW	BC857BDW1T1G	BC860C
BC847BPDV6T1G	BC850C	BC857BM	BC860CW
BC847BPN	BC850CW	BC857BMB	BC868
BC847BS	BC856	BC857BS	BC868-25
BC847BT	BC856A	BC857BT	BC869
BC847BV	BC856ALT1G	BC857BV	BC869-16
BC847BVN	BC856AT	BC857BW	BC869-25
BC847BW	BC856AW	BC857C	BCD_7SEG_DCD
BC847C	BC856B	BC857CM	BCM61B
BC847CDXV6T1G	BC856BDW1T1G	BC857CMB	BCM62B
BC847CM	BC856BDW1T3G	BC857CT	BCM847BS
BC847CMB	BC856BS	BC857CW	BCM847BV
BC847CT	BC856BT	BC857T	BCM847DS
BC847CTT1G	BC856BW	BC857W	BCM856BS
BC847CW	BC856BWT1G	BC858A	BCM856DS
BC847DS	BC856S	BC858B	BCM857BS
BC847T	BC856T	BC858W	BCM857BV
BC847W	BC856W	BC859A	BCM857DS
BC848B	BC857	BC859B	BCP49

Multisim 14.0 Base Components

BCP51	BCP56T3G	BCR133W	BCR185S
BCP51-10	BCP68	BCR135	BCR185W
BCP51-16	BCP68-25	BCR135S	BCR191
BCP52	BCP68T1G	BCR135W	BCR191W
BCP52-10	BCP69	BCR141	BCR192
BCP52-16	BCP69-16	BCR141S	BCR192W
BCP53	BCP69-25	BCR141W	BCR196
BCP53-10	BCP69T1G	BCR142	BCR196W
BCP53-16	BCR08PN	BCR142W	BCR198
BCP54	BCR108	BCR146	BCR198S
BCP54-10	BCR108S	BCR148	BCR198W
BCP54-16	BCR108W	BCR148S	BCR22PN
BCP55	BCR10PN	BCR148W	BCR35PN
BCP55-10	BCR112	BCR158	BCR48PN
BCP55-16	BCR112W	BCR158W	BCR503
BCP56	BCR116	BCR162	BCR505
BCP56-10	BCR116S	BCR166	BCR512
BCP56-10T1	BCR116W	BCR166W	BCR521
BCP56-10T1G	BCR119	BCR169	BCR523
BCP56-16	BCR119S	BCR169S	BCR523U
BCP56-16T1	BCR119W	BCR169W	BCR533
BCP56-16T1G	BCR129	BCR183	BCR553
BCP56-16T3G	BCR129W	BCR183S	BCR555
BCP56T1	BCR133	BCR183W	BCR562
BCP56T1G	BCR133S	BCR185	BCR573

Multisim 14.0 Base Components

BCR583	BCW31	BCX42	BCX71J
BCV26	BCW32	BCX51	BCX71K
BCV27	BCW33	BCX51-10	BD135
BCV28	BCW60B	BCX51-16	BD135G
BCV29	BCW60C	BCX52	BD136
BCV46	BCW60D	BCX52-10	BD136G
BCV47	BCW61A	BCX52-16	BD137
BCV48	BCW61B	BCX53	BD137G
BCV49	BCW61C	BCX53-10	BD138
BCV61	BCW61D	BCX53-16	BD138G
BCV61A	BCW65A	BCX54	BD139
BCV61B	BCW66F	BCX54-10	BD139G
BCV61C	BCW67A	BCX54-16	BD140
BCV62	BCW68F	BCX55	BD140G
BCV62A	BCW69	BCX55-10	BD159G
BCV62B	BCW70	BCX55-16	BD179G
BCV62C	BCW71	BCX56	BD180G
BCV63	BCW72	BCX56-10	BD234G
BCV63B	BCW89	BCX56-16	BD237G
BCV64B	BCX17	BCX70G	BD241CG
BCV65	BCX17LT1G	BCX70H	BD242BG
BCV71	BCX18	BCX70J	BD242CG
BCV72	BCX19	BCX70K	BD243CG
BCW29	BCX38B	BCX71G	BD244BG
BCW30	BCX41	BCX71H	BD244CG

Multisim 14.0 Base Components

BD436TG	BD810G	BF256A	BF723
BD437G	BDP947	BF256B	BF799
BD437TG	BDP948	BF410A	BF820
BD438G	BDP949	BF410B	BF820W
BD439G	BDP950	BF410C	BF821
BD440G	BDP953	BF410D	BF822
BD441G	BDP954	BF422G	BF823
BD442G	BDV64BG	BF510	BF824
BD675AG	BDV65BG	BF511	BF824W
BD675G	BDW42G	BF512	BF840
BD676AG	BDW46G	BF513	BF851A
BD676G	BDW47G	BF517	BF851B
BD677AG	BDX33BG	BF545A	BF851C
BD677G	BDX33CG	BF545B	BF861A
BD678AG	BDX34BG	BF545C	BF861B
BD678G	BDX34CG	BF550	BF861C
BD679AG	BDX53BG	BF556A	BF904
BD679G	BDX53CG	BF556B	BF904R
BD680AG	BDX54BG	BF570	BF904WR
BD680G	BDX54CG	BF620	BF908WR
BD681G	BF245A	BF621	BF909
BD682G	BF245B	BF622	BF909R
BD787G	BF245C	BF623	BF909WR
BD788G	BF246A	BF720	BF998
BD809G	BF247A	BF722	BF998R

Multisim 14.0 Base Components

BF998WR	BFU310	BPW 34	BSC011N03LS
BFG135A	BFW10	BPW 34 FA	BSC011N03LSI
BFG193	BFW11	BPW 34 FAS	BSC014N03LS G
BFG194	BFW12	BPW 34 FASR	BSC014N03MS G
BFN18	BFW13	BRUSHLESS_DC_M ACHINE	BSC014N04LS
BFN19	BFW61		BSC014N04LSI
BFN24	BICOLOR_LED_Red/ Green	BS170	BSC014N06NS
BFN26		BSB008NE2LX	BSC014NE2LSI
BFN27	BICOLOR_LED_Red- Orange/Green	BSB012N03LX3 G	BSC016N03LS G
BFN39	BIPOLAR_CURRENT	BSB012NE2LX	BSC016N03MS G
BFP194	BIPOLAR_VOLTAGE	BSB012NE2LXI	BSC016N04LS G
BFQ31	BJT_LPNP	BSB013NE2LXI	BSC016N06NS
BFR194	BJT_NPN	BSB014N04LX3 G	BSC017N04NS G
BFR30	BJT_NPN_4T	BSB015N04NX3 G	BSC018N04LS G
BFR31	BJT_PNP	BSB017N03LX3 G	BSC018NE2LS
BFS17	BJT_PNP_4T	BSB028N06NN3 G	BSC018NE2LSI
BFS17H	BOOST_CONVERTE R	BSB044N08NN3 G	BSC019N02KS G
BFS17P		BSB056N10NN3 G	BSC019N04LS
BFS19	BOSCH-EDC16- BDM-HDR	BSB165N15NZ3 G	BSC019N04NS G
BFS20		BSB280N15NZ3 G	BSC020N03LS G
BFS20W	BPASS	BSC009NE2LS	BSC020N03MS G
BFS60	BPV10NF	BSC010N04LS	BSC022N04LS
BFT46	BPV22NF	BSC010N04LSI	BSC024NE2LS
BFU308	BPV23F	BSC010NE2LS	BSC025N03LS G
BFU309	BPV23NF	BSC010NE2LSI	BSC025N03MS G

Multisim 14.0 Base Components

BSC026N02KS G	BSC050NE2LS	BSC0902NSI	BSC123N08NS3 G
BSC026N04LS	BSC052N03LS	BSC0904NSI	BSC123N10LS G
BSC027N04LS G	BSC054N04NS G	BSC0906NS	BSC12DN20NS3 G
BSC028N06LS3 G	BSC057N03LS G	BSC0908NS	BSC130P03LS G
BSC028N06NS	BSC057N03MS G	BSC0909NS	BSC150N03LD G
BSC030N03LS G	BSC057N08NS3 G	BSC090N03LS G	BSC152N10NSF G
BSC030N03MS G	BSC059N04LS G	BSC090N03MS G	BSC159N10LSF G
BSC030N04NS G	BSC060N10NS3 G	BSC0910NDI	BSC160N10NS3 G
BSC030P03NS3 G	BSC060P03NS3E G	BSC0911ND	BSC16DN25NS3 G
BSC031N06NS3 G	BSC066N06NS	BSC0921NDI	BSC190N12NS3 G
BSC032N04LS	BSC067N06LS3 G	BSC0923NDI	BSC190N15NS3 G
BSC032NE2LS	BSC070N10NS3 G	BSC0924NDI	BSC196N10NS G
BSC034N06NS	BSC072N03LD G	BSC0925ND	BSC200P03LS G
BSC035N04LS G	BSC076N06NS3 G	BSC093N04LS G	BSC205N10LS G
BSC036NE7NS3 G	BSC077N12NS3 G	BSC097N06NS	BSC22DN20NS3 G
BSC039N06NS	BSC079N10NS G	BSC100N03LS G	BSC240N12NS3 G
BSC042N03LS G	BSC080N03LS G	BSC100N03MS G	BSC252N10NSF G
BSC042N03MS G	BSC080N03MS G	BSC100N06LS3 G	BSC265N10LSF G
BSC042NE7NS3 G	BSC080P03LS G	BSC100N10NSF G	BSC320N20NS3 G
BSC046N02KS G	BSC082N10LS G	BSC105N10LSF G	BSC340N08NS3 G
BSC046N10NS3 G	BSC084P03NS3 G	BSC109N10NS3 G	BSC360N15NS3 G
BSC047N08NS3 G	BSC084P03NS3E G	BSC110N06NS3 G	BSC440N10NS3 G
BSC050N03LS G	BSC0901NS	BSC118N10NS G	BSC500N20NS3 G
BSC050N03MS G	BSC0901NSI	BSC120N03LS G	BSC520N15NS3 G
BSC050N04LS G	BSC0902NS	BSC120N03MS G	BSC600N25NS3 G

Multisim 14.0 Base Components

BSC750N10ND G	BSH202	BSN045NE2LS	BSO613SPV G
BSC900N20NS3 G	BSH203	BSN048N03LS	BSP 60 E6327
BSD214	BSH205	BSN20	BSP030
BSD214SN	BSH207	BSO033N03MS G	BSP100
BSD215	BSJ108	BSO040N03MS G	BSP110
BSD223P	BSJ109	BSO051N03MS G	BSP123
BSD235N	BSJ110	BSO065N03MS G	BSP125
BSD314SPE	BSL202SN	BSO080P03NS3 G	BSP129
BSD316SN	BSL205N	BSO080P03NS3E G	BSP135
BSD816SN	BSL207N	BSO080P03S H	BSP149
BSD840N	BSL207SP	BSO083N03MS G	BSP16T1G
BSE-080-01-L-D-A	BSL211SP	BSO110N03MS G	BSP170P
BSF024N03LT3 G	BSL214N	BSO130N03MS G	BSP171P
BSF030NE2LQ	BSL302SN	BSO130P03S H	BSP19
BSF035NE2LQ	BSL306N	BSO150N03MD G	BSP19AT1G
BSF050N03LQ3 G	BSL307SP	BSO200P03S H	BSP204
BSF134N10NJ3 G	BSL308PE	BSO201SP H	BSP204A
BSF450NE7NH3 G	BSL314PE	BSO203SP H	BSP205
BSH103	BSL606SN	BSO207P H	BSP206
BSH105	BSL802SN	BSO211P H	BSP230
BSH108	BSL806N	BSO220N03MD G	BSP250
BSH111	BSN011NE2LS	BSO220N03MS G	BSP296
BSH114	BSN011NE2LSI	BSO301SP H	BSP297
BSH121	BSN012N03LS	BSO303SP H	BSP304
BSH201	BSN012N03LSI	BSO330N02K G	BSP304A

Multisim 14.0 Base Components

BSP31	BSR30	BSS138N	BSS7728N
BSP315P	BSR302N	BSS138P	BSS806N
BSP316P	BSR31	BSS138PS	BSS816NW
BSP317P	BSR315P	BSS138PW	BSS83
BSP32	BSR316P	BSS138W	BSS83P
BSP324	BSR33	BSS139	BSS84
BSP33	BSR41	BSS159N	BSS84AK
BSP41	BSR43	BSS169	BSS84AKM
BSP43	BSR56	BSS192	BSS84AKMB
BSP50	BSR57	BSS192P	BSS84AKS
BSP51	BSR58	BSS205N	BSS84AKT
BSP52	BSR606N	BSS209PW	BSS84AKV
BSP52T1G	BSR802N	BSS214N	BSS84AKW
BSP52T3G	BSR92P	BSS214NW	BSS84LT1G
BSP60	BSS110	BSS223PW	BSS84P
BSP61	BSS123	BSS225	BSS84PW
BSP613P	BSS123LT1G	BSS306N	BSS84PW H6327
BSP62	BSS126	BSS308PE	BSS87
BSP88	BSS127	BSS314PE	BSS92
BSP89	BSS131	BSS315P	BST100
BSP92P	BSS138BK	BSS316N	BST110
BSR14	BSS138BKS	BSS606N	BST120
BSR16	BSS138BKW	BSS63	BST122
BSR19A	BSS138LT1G	BSS64	BST39
BSR202N	BSS138LT3G	BSS670S2L	BST50

Multisim 14.0 Base Components

BST51	BSZ050N03MS G	BSZ105N04NS G	BT134-G
BST52	BSZ058N03LS G	BSZ110N06NS3 G	BT134W
BST60	BSZ058N03MS G	BSZ120P03NS3 G	BT136
BST61	BSZ060NE2LS	BSZ120P03NS3E G	BT136-E
BST62	BSZ065N03LS	BSZ123N08NS3 G	BT136-F
BST82	BSZ067N06LS3 G	BSZ12DN20NS3 G	BT136-G
BSV236SP	BSZ068N06NS	BSZ130N03LS G	BT137
BSV52	BSZ076N06NS3 G	BSZ130N03MS G	BT137-E
BSV78	BSZ086P03NS3 G	BSZ150N10LS3 G	BT137-F
BSV79	BSZ086P03NS3E G	BSZ160N10NS3 G	BT137-G
BSV80	BSZ088N03LS G	BSZ165N04NS G	BT138
BSV81	BSZ088N03MS G	BSZ16DN25NS3 G	BT138-E
BSZ018NE2LS	BSZ0901NS	BSZ180P03NS3 G	BT138-F
BSZ018NE2LSI	BSZ0901NSI	BSZ180P03NS3E G	BT138-G
BSZ019N03LS	BSZ0902NS	BSZ22DN20NS3 G	BT139
BSZ023N04LS	BSZ0902NSI	BSZ240N12NS3 G	BT139-E
BSZ028N04LS	BSZ0904NSI	BSZ340N08NS3 G	BT139-F
BSZ034N04LS	BSZ0907ND	BSZ42DN25NS3 G	BT139-G
BSZ035N03LS G	BSZ0908ND	BSZ440N10NS3 G	BT145_500R
BSZ035N03MS G	BSZ0909NS	BSZ520N15NS3 G	BT148_400R
BSZ036NE2LS	BSZ097N04LS G	BSZ900N15NS3 G	BT148W_400R
BSZ040N04LS G	BSZ100N03LS G	BSZ900N20NS3 G	BT149_B
BSZ042N04NS G	BSZ100N03MS G	BT134	BT150_500R
BSZ042N06NS	BSZ100N06LS3 G	BT134-E	BT151_500R
BSZ050N03LS G	BSZ100N06NS	BT134-F	BT152_400R

Multisim 14.0 Base Components

BT153_500R	BUF602ID	BY706	BYD13M
BT169_B	BUF602IDBVR	BY710	BYD14D
BTA140	BUFFER	BY711	BYD14G
BTW38_600R	BUH100G	BY712	BYD14J
BTW40_400R	BUH150G	BY713	BYD14K
BTW42_600R	BUH50G	BY714	BYD14M
BTW43	BUL45D2G	BY715	BYD17D
BTW45_400R	BUL45G	BY716	BYD17G
BTY79_400R	BUV21G	BY717	BYD17J
BTY91_400R	BUV22G	BY718	BYD17K
BU323ZG	BUV26G	BY719	BYD17M
BU406G	BUX85G	BY720	BYD31D
BUB323ZG	BUZZER	BY721	BYD31G
BUB323ZT4G	BVSS123LT1G	BY722	BYD31J
BUCK_BOOST_CONVERTER	BVSS138LT1G	BY723	BYD33D
BUCK_CONVERTER	BY228	BYD11	BYD33G
BUD42D-1G	BY328	BYD11D	BYD33J
BUD42DT4G	BY438	BYD11G	BYD33K
BUF	BY448	BYD11J	BYD33M
BUF_3S_AHOE	BY458	BYD11K	BYD34D
BUF_3S_ALOE	BY505	BYD11M	BYD34G
BUF_CO	BY527	BYD13D	BYD34J
BUF_INV	BY584	BYD13G	BYD34K
BUF601AP	BY627	BYD13J	BYD34M
	BY705	BYD13K	BYD37D

Multisim 14.0 Base Components

BYD37G	BYG10G-E3/TR	BYM26B	BYV27-100
BYD37J	BYG10J-E3/TR	BYM26C	BYV27-50
BYD37K	BYG20J-E3/TR	BYM26D	BYV28-100
BYD37M	BYG21M-E3/TR	BYM26E	BYV28-150
BYD73A	BYG22D-E3/TR	BYM36A	BYV28-200
BYD73B	BYG24J-E3/TR3	BYM36B	BYV28-50
BYD73C	BYM10-100	BYM36C	BYV32-200G
BYD73D	BYM10-1000	BYM36D	BYV36A
BYD73E	BYM10-1000-E3/97	BYM36E	BYV36B
BYD73F	BYM10-200	BYM56A	BYV36C
BYD73G	BYM10-400	BYM56B	BYV36D
BYD74A	BYM10-50	BYM56C	BYV36E
BYD74B	BYM10-600	BYM56D	BYV95A
BYD74C	BYM10-800	BYM56E	BYV95B
BYD74D	BYM11-100	BYS10-45-E3/TR	BYV95C
BYD74E	BYM11-1000	BYS11-90-E3/TR	BYV96D
BYD74F	BYM11-1000-E3/96	BYT28-300-E3/45	BYV96E
BYD74G	BYM11-100-E3/96	BYV10-20	BYW29-200G
BYD77A	BYM11-200	BYV10-30	BYW51-200G
BYD77B	BYM11-400	BYV10-40	BYW54
BYD77C	BYM11-50	BYV26A	BYW55
BYD77D	BYM11-600	BYV26B	BYW56
BYD77E	BYM11-800	BYV26C	BYW80-200G
BYD77F	BYM12-400-E3/96	BYV26D	BYW95A
BYD77G	BYM26A	BYV26E	BYW95B

Multisim 14.0 Base Components

BYW95C	BZA968AVL	BZB84-B13	BZB84-B5V6
BYW96D	BZB100A	BZB84-B15	BZB84-B62
BYW96E	BZB784-C10	BZB84-B16	BZB84-B68
BYX10G	BZB784-C11	BZB84-B18	BZB84-B6V2
BYX110GP	BZB784-C12	BZB84-B20	BZB84-B6V8
BZA408B	BZB784-C13	BZB84-B22	BZB84-B75
BZA418A	BZB784-C15	BZB84-B24	BZB84-B7V5
BZA420A	BZB784-C2V4	BZB84-B27	BZB84-B8V2
BZA456A	BZB784-C2V7	BZB84-B2V4	BZB84-B9V1
BZA462A	BZB784-C3V0	BZB84-B2V7	BZB84-C10
BZA820A	BZB784-C3V3	BZB84-B30	BZB84-C11
BZA856A	BZB784-C3V6	BZB84-B33	BZB84-C12
BZA856AL	BZB784-C3V9	BZB84-B36	BZB84-C13
BZA856AVL	BZB784-C4V3	BZB84-B39	BZB84-C15
BZA862A	BZB784-C4V7	BZB84-B3V0	BZB84-C16
BZA862AL	BZB784-C5V1	BZB84-B3V3	BZB84-C18
BZA862AVL	BZB784-C5V6	BZB84-B3V6	BZB84-C20
BZA868A	BZB784-C6V2	BZB84-B3V9	BZB84-C22
BZA868AL	BZB784-C6V8	BZB84-B43	BZB84-C24
BZA868AVL	BZB784-C7V5	BZB84-B47	BZB84-C27
BZA956A	BZB784-C8V2	BZB84-B4V3	BZB84-C2V4
BZA956AVL	BZB784-C9V1	BZB84-B4V7	BZB84-C2V7
BZA962A	BZB84-B10	BZB84-B51	BZB84-C30
BZA962AVL	BZB84-B11	BZB84-B56	BZB84-C33
BZA968A	BZB84-B12	BZB84-B5V1	BZB84-C36

Multisim 14.0 Base Components

BZB84-C39	BZB984-C15	BZT52H-B24	BZT52H-C12
BZB84-C3V0	BZB984-C2V4	BZT52H-B27	BZT52H-C13
BZB84-C3V3	BZB984-C2V7	BZT52H-B2V4	BZT52H-C15
BZB84-C3V6	BZB984-C3V0	BZT52H-B2V7	BZT52H-C16
BZB84-C3V9	BZB984-C3V3	BZT52H-B30	BZT52H-C18
BZB84-C43	BZB984-C3V6	BZT52H-B33	BZT52H-C20
BZB84-C47	BZB984-C3V9	BZT52H-B36	BZT52H-C22
BZB84-C4V3	BZB984-C4V3	BZT52H-B39	BZT52H-C24
BZB84-C4V7	BZB984-C4V7	BZT52H-B3V0	BZT52H-C27
BZB84-C51	BZB984-C5V1	BZT52H-B43	BZT52H-C2V4
BZB84-C56	BZB984-C5V6	BZT52H-B47	BZT52H-C2V7
BZB84-C5V1	BZB984-C6V2	BZT52H-B51	BZT52H-C30
BZB84-C5V6	BZB984-C6V8	BZT52H-B56	BZT52H-C33
BZB84-C62	BZB984-C7V5	BZT52H-B5V1	BZT52H-C36
BZB84-C68	BZB984-C8V2	BZT52H-B5V6	BZT52H-C39
BZB84-C6V2	BZB984-C9V1	BZT52H-B62	BZT52H-C3V0
BZB84-C6V8	BZT52H-B10	BZT52H-B68	BZT52H-C3V6
BZB84-C75	BZT52H-B11	BZT52H-B6V2	BZT52H-C3V9
BZB84-C7V5	BZT52H-B12	BZT52H-B6V8	BZT52H-C43
BZB84-C8V2	BZT52H-B13	BZT52H-B75	BZT52H-C47
BZB84-C9V1	BZT52H-B15	BZT52H-B7V5	BZT52H-C4V3
BZB984-C10	BZT52H-B16	BZT52H-B8V2	BZT52H-C4V7
BZB984-C11	BZT52H-B18	BZT52H-B9V1	BZT52H-C51
BZB984-C12	BZT52H-B20	BZT52H-C10	BZT52H-C56
BZB984-C13	BZT52H-B22	BZT52H-C11	BZT52H-C5V1

Multisim 14.0 Base Components

BZT52H-C5V6	BZV55-B30	BZV55-C12	BZV60-B10
BZT52H-C62	BZV55-B33	BZV55-C13	BZV60-B11
BZT52H-C68	BZV55-B36	BZV55-C15	BZV60-B12
BZT52H-C6V2	BZV55-B39	BZV55-C16	BZV60-B13
BZT52H-C6V8	BZV55-B3V0	BZV55-C18	BZV60-B15
BZT52H-C75	BZV55-B3V3	BZV55-C27	BZV60-B16
BZT52H-C7V5	BZV55-B3V6	BZV55-C2V4	BZV60-B18
BZT52H-C8V2	BZV55-B3V9	BZV55-C2V7	BZV60-B20
BZT52H-C9V1	BZV55-B43	BZV55-C33	BZV60-B22
BZV49-C12	BZV55-B47	BZV55-C3V0	BZV60-B24
BZV49-C16	BZV55-B4V3	BZV55-C3V3	BZV60-B27
BZV49-C3V6	BZV55-B4V7	BZV55-C3V6	BZV60-B2V4
BZV55-B10	BZV55-B51	BZV55-C3V9	BZV60-B2V7
BZV55-B11	BZV55-B56	BZV55-C43	BZV60-B30
BZV55-B12	BZV55-B5V1	BZV55-C47	BZV60-B33
BZV55-B13	BZV55-B5V6	BZV55-C4V3	BZV60-B36
BZV55-B15	BZV55-B68	BZV55-C4V7	BZV60-B39
BZV55-B16	BZV55-B6V2	BZV55-C5V1	BZV60-B3V0
BZV55-B18	BZV55-B6V8	BZV55-C5V6	BZV60-B3V3
BZV55-B20	BZV55-B75	BZV55-C6V2	BZV60-B3V6
BZV55-B22	BZV55-B7V5	BZV55-C6V8	BZV60-B3V9
BZV55-B24	BZV55-B8V2	BZV55-C7V5	BZV60-B43
BZV55-B27	BZV55-B9V1	BZV55-C8V2	BZV60-B47
BZV55-B2V4	BZV55-C10	BZV55-C9V1	BZV60-B4V3
BZV55-B2V7	BZV55-C11	BZV55-F2V4	BZV60-B4V7

Multisim 14.0 Base Components

BZV60-B51	BZV60-C30	BZV85-C10	BZV85-C68
BZV60-B56	BZV60-C33	BZV85-C11	BZV85-C6V2
BZV60-B5V1	BZV60-C36	BZV85-C12	BZV85-C6V8
BZV60-B5V6	BZV60-C39	BZV85-C13	BZV85-C75
BZV60-B62	BZV60-C3V0	BZV85-C15	BZV85-C7V5
BZV60-B68	BZV60-C3V3	BZV85-C16	BZV85-C8V2
BZV60-B6V2	BZV60-C3V6	BZV85-C18	BZV86-1V4
BZV60-B6V8	BZV60-C3V9	BZV85-C20	BZV86-2V0
BZV60-B75	BZV60-C43	BZV85-C22	BZV86-2V6
BZV60-B7V5	BZV60-C47	BZV85-C24	BZV86-3V2
BZV60-B8V2	BZV60-C4V3	BZV85-C27	BZV90-C10
BZV60-B9V1	BZV60-C4V7	BZV85-C30	BZV90-C11
BZV60-C10	BZV60-C51	BZV85-C33	BZV90-C12
BZV60-C11	BZV60-C56	BZV85-C36	BZV90-C13
BZV60-C12	BZV60-C5V1	BZV85-C39	BZV90-C15
BZV60-C13	BZV60-C5V6	BZV85-C3V6	BZV90-C16
BZV60-C15	BZV60-C62	BZV85-C3V9	BZV90-C18
BZV60-C16	BZV60-C68	BZV85-C43	BZV90-C20
BZV60-C18	BZV60-C6V2	BZV85-C47	BZV90-C22
BZV60-C20	BZV60-C6V8	BZV85-C4V3	BZV90-C24
BZV60-C22	BZV60-C75	BZV85-C4V7	BZV90-C27
BZV60-C24	BZV60-C7V5	BZV85-C51	BZV90-C2V4
BZV60-C27	BZV60-C8V2	BZV85-C5V1	BZV90-C2V7
BZV60-C2V4	BZV60-C9V1	BZV85-C5V6	BZV90-C30
BZV60-C2V7	BZV80	BZV85-C62	BZV90-C33

Multisim 14.0 Base Components

BZV90-C36	BZW03-C110	BZW03-C51	BZX384-B33
BZV90-C39	BZW03-C12	BZW03-C56	BZX384-B36
BZV90-C3V0	BZW03-C120	BZW03-C62	BZX384-B39
BZV90-C3V3	BZW03-C13	BZW03-C68	BZX384-B3V0
BZV90-C3V6	BZW03-C130	BZW03-C75	BZX384-B3V3
BZV90-C3V9	BZW03-C15	BZW03-C7V5	BZX384-B3V6
BZV90-C43	BZW03-C150	BZW03-C82	BZX384-B3V9
BZV90-C47	BZW03-C16	BZW03-C8V2	BZX384-B43
BZV90-C4V3	BZW03-C160	BZW03-C91	BZX384-B47
BZV90-C4V7	BZW03-C18	BZW03-C9V1	BZX384-B4V3
BZV90-C51	BZW03-C180	BZX100A	BZX384-B4V7
BZV90-C56	BZW03-C20	BZX384-B10	BZX384-B51
BZV90-C5V1	BZW03-C200	BZX384-B11	BZX384-B56
BZV90-C5V6	BZW03-C22	BZX384-B12	BZX384-B5V1
BZV90-C62	BZW03-C220	BZX384-B13	BZX384-B5V6
BZV90-C68	BZW03-C24	BZX384-B15	BZX384-B62
BZV90-C6V2	BZW03-C240	BZX384-B16	BZX384-B68
BZV90-C6V8	BZW03-C27	BZX384-B18	BZX384-B6V2
BZV90-C75	BZW03-C270	BZX384-B20	BZX384-B6V8
BZV90-C7V5	BZW03-C30	BZX384-B22	BZX384-B75
BZV90-C8V2	BZW03-C33	BZX384-B24	BZX384-B7V5
BZV90-C9V1	BZW03-C36	BZX384-B27	BZX384-B8V2
BZW03-C10	BZW03-C39	BZX384-B2V4	BZX384-B9V1
BZW03-C100	BZW03-C43	BZX384-B2V7	BZX384-C10
BZW03-C11	BZW03-C47	BZX384-B30	BZX384-C11

Multisim 14.0 Base Components

BZX384-C12	BZX384-C6V2	BZX55C3V6	BZX585-B16
BZX384-C13	BZX384-C6V8	BZX55C3V9	BZX585-B18
BZX384-C16	BZX384-C75	BZX55C43	BZX585-B20
BZX384-C20	BZX384-C7V5	BZX55C47	BZX585-B22
BZX384-C22	BZX384-C8V2	BZX55C4V3	BZX585-B24
BZX384-C24	BZX384-C9V1	BZX55C4V7	BZX585-B27
BZX384-C2V4	BZX55C10	BZX55C51	BZX585-B2V4
BZX384-C2V7	BZX55C11	BZX55C56	BZX585-B2V7
BZX384-C30	BZX55C12	BZX55C5V1	BZX585-B30
BZX384-C33	BZX55C13	BZX55C5V6	BZX585-B33
BZX384-C36	BZX55C15	BZX55C62	BZX585-B36
BZX384-C39	BZX55C16	BZX55C68	BZX585-B39
BZX384-C3V0	BZX55C18	BZX55C6V2	BZX585-B3V0
BZX384-C3V3	BZX55C20	BZX55C6V8	BZX585-B3V3
BZX384-C3V6	BZX55C22	BZX55C75	BZX585-B3V6
BZX384-C3V9	BZX55C24	BZX55C7V5	BZX585-B3V9
BZX384-C43	BZX55C27	BZX55C82	BZX585-B43
BZX384-C47	BZX55C2V4	BZX55C8V2	BZX585-B47
BZX384-C4V3	BZX55C2V7	BZX55C91	BZX585-B4V3
BZX384-C4V7	BZX55C30	BZX55C9V1	BZX585-B4V7
BZX384-C51	BZX55C33	BZX585-B10	BZX585-B51
BZX384-C56	BZX55C36	BZX585-B11	BZX585-B56
BZX384-C5V1	BZX55C39	BZX585-B12	BZX585-B5V1
BZX384-C62	BZX55C3V0	BZX585-B13	BZX585-B5V6
BZX384-C68	BZX55C3V3	BZX585-B15	BZX585-B62

Multisim 14.0 Base Components

BZX585-B68	BZX585-C43	BZX79-A27	BZX79-A8V2
BZX585-B6V2	BZX585-C47	BZX79-A2V4	BZX79-A9V1
BZX585-B6V8	BZX585-C4V3	BZX79-A2V7	BZX79-B10
BZX585-B75	BZX585-C4V7	BZX79-A30	BZX79-B11
BZX585-B7V5	BZX585-C51	BZX79-A33	BZX79-B12
BZX585-B8V2	BZX585-C56	BZX79-A36	BZX79-B13
BZX585-B9V1	BZX585-C5V1	BZX79-A3V0	BZX79-B15
BZX585-C10	BZX585-C62	BZX79-A3V3	BZX79-B16
BZX585-C11	BZX585-C68	BZX79-A3V6	BZX79-B18
BZX585-C12	BZX585-C6V2	BZX79-A3V9	BZX79-B20
BZX585-C13	BZX585-C6V8	BZX79-A40	BZX79-B22
BZX585-C16	BZX585-C75	BZX79-A43	BZX79-B24
BZX585-C20	BZX585-C7V5	BZX79-A47	BZX79-B27
BZX585-C22	BZX585-C8V2	BZX79-A4V3	BZX79-B2V4
BZX585-C24	BZX585-C9V1	BZX79-A4V7	BZX79-B2V7
BZX585-C2V4	BZX79-A10	BZX79-A51	BZX79-B30
BZX585-C2V7	BZX79-A11	BZX79-A56	BZX79-B33
BZX585-C30	BZX79-A12	BZX79-A5V1	BZX79-B36
BZX585-C33	BZX79-A13	BZX79-A5V6	BZX79-B39
BZX585-C36	BZX79-A15	BZX79-A62	BZX79-B3V3
BZX585-C39	BZX79-A16	BZX79-A68	BZX79-B3V6
BZX585-C3V0	BZX79-A18	BZX79-A6V2	BZX79-B3V9
BZX585-C3V3	BZX79-A20	BZX79-A6V8	BZX79-B43
BZX585-C3V6	BZX79-A22	BZX79-A75	BZX79-B47
BZX585-C3V9	BZX79-A24	BZX79-A7V5	BZX79-B4V3

Multisim 14.0 Base Components

BZX79-B4V7	BZX79-C180	BZX79-C68	BZX83-C3V6
BZX79-B51	BZX79-C20	BZX79-C6V2	BZX83-C3V9
BZX79-B56	BZX79-C200	BZX79-C6V8	BZX83-C4V3
BZX79-B5V1	BZX79-C22	BZX79-C75	BZX83-C4V7
BZX79-B62	BZX79-C24	BZX79-C7V5	BZX83-C5V1
BZX79-B68	BZX79-C27	BZX79-C82	BZX83-C5V6
BZX79-B6V2	BZX79-C2V4	BZX79-C8V2	BZX83-C6V2
BZX79-B6V8	BZX79-C2V7	BZX79-C91	BZX83-C6V8
BZX79-B75	BZX79-C30	BZX79-C9V1	BZX83-C7V5
BZX79-B7V5	BZX79-C33	BZX83-C10	BZX83-C8V2
BZX79-B8V2	BZX79-C36	BZX83-C11	BZX83-C9V1
BZX79-B9V1	BZX79-C39	BZX83-C12	BZX84-A10
BZX79-C10	BZX79-C3V0	BZX83-C13	BZX84-A11
BZX79-C100	BZX79-C3V3	BZX83-C15	BZX84-A12
BZX79-C11	BZX79-C3V6	BZX83-C16	BZX84-A13
BZX79-C110	BZX79-C3V9	BZX83-C18	BZX84-A15
BZX79-C12	BZX79-C43	BZX83-C20	BZX84-A16
BZX79-C120	BZX79-C47	BZX83-C22	BZX84-A18
BZX79-C13	BZX79-C4V3	BZX83-C24	BZX84-A20
BZX79-C130	BZX79-C4V7	BZX83-C27	BZX84-A22
BZX79-C15	BZX79-C51	BZX83-C2V7	BZX84-A24
BZX79-C150	BZX79-C56	BZX83-C30	BZX84-A27
BZX79-C16	BZX79-C5V1	BZX83-C33	BZX84-A2V4
BZX79-C160	BZX79-C5V6	BZX83-C3V0	BZX84-A2V7
BZX79-C18	BZX79-C62	BZX83-C3V3	BZX84-A30

Multisim 14.0 Base Components

BZX84-A33	BZX84-B12	BZX84-B51	BZX84C15LT1
BZX84-A36	BZX84-B13	BZX84-B56	BZX84C15LT1G
BZX84-A39	BZX84-B15	BZX84-B5V1	BZX84C15LT3G
BZX84-A3V0	BZX84-B16	BZX84B5V1LT1G	BZX84-C16
BZX84-A3V3	BZX84B16LT1G	BZX84-B5V6	BZX84-C18
BZX84-A3V6	BZX84-B18	BZX84B5V6LT1G	BZX84-C20
BZX84-A3V9	BZX84-B20	BZX84-B62	BZX84-C22
BZX84-A43	BZX84-B22	BZX84-B68	BZX84-C24
BZX84-A47	BZX84-B24	BZX84-B6V2	BZX84-C27
BZX84-A4V3	BZX84-B27	BZX84B6V2LT1G	BZX84-C2V4
BZX84-A4V7	BZX84-B2V4	BZX84-B6V8	BZX84-C2V7
BZX84-A51	BZX84-B2V7	BZX84B6V8LT1G	BZX84-C30
BZX84-A56	BZX84-B30	BZX84-B75	BZX84-C33
BZX84-A5V1	BZX84-B33	BZX84-B7V5	BZX84C33LT1G
BZX84-A5V6	BZX84-B36	BZX84B7V5LT1G	BZX84C33LT3G
BZX84-A62	BZX84-B39	BZX84-B8V2	BZX84-C36
BZX84-A68	BZX84-B3V0	BZX84B8V2LT1G	BZX84C36LT1G
BZX84-A6V2	BZX84-B3V3	BZX84-B9V1	BZX84-C39
BZX84-A6V8	BZX84-B3V6	BZX84B9V1LT1G	BZX84-C3V0
BZX84-A75	BZX84-B3V9	BZX84-C10	BZX84C3V0LT1G
BZX84-A7V5	BZX84-B43	BZX84-C11	BZX84-C3V3
BZX84-A8V2	BZX84-B47	BZX84-C12	BZX84-C3V6
BZX84-A9V1	BZX84-B4V3	BZX84C12LT1G	BZX84-C3V9
BZX84-B10	BZX84-B4V7	BZX84-C13	BZX84-C43
BZX84-B11	BZX84B4V7LT1G	BZX84-C15	BZX84-C47

Multisim 14.0 Base Components

BZX84-C4V3	BZX84-C8V2	BZX84J-B3V9	BZX84J-C22
BZX84-C4V7	BZX84C8V2LT1G	BZX84J-B43	BZX84J-C24
BZX84C4V7LT1G	BZX84-C9V1	BZX84J-B47	BZX84J-C27
BZX84C4V7LT3G	BZX84C9V1LT1G	BZX84J-B4V3	BZX84J-C2V4
BZX84-C51	BZX84C9V1LT3G	BZX84J-B4V7	BZX84J-C2V7
BZX84-C56	BZX84J-B10	BZX84J-B51	BZX84J-C30
BZX84-C5V1	BZX84J-B11	BZX84J-B56	BZX84J-C33
BZX84C5V1LT1G	BZX84J-B12	BZX84J-B5V1	BZX84J-C36
BZX84C5V1LT3G	BZX84J-B13	BZX84J-B5V6	BZX84J-C39
BZX84-C5V6	BZX84J-B15	BZX84J-B62	BZX84J-C3V0
BZX84C5V6LT1G	BZX84J-B16	BZX84J-B68	BZX84J-C3V3
BZX84C5V6LT3G	BZX84J-B18	BZX84J-B6V2	BZX84J-C3V6
BZX84-C62	BZX84J-B20	BZX84J-B6V8	BZX84J-C3V9
BZX84-C68	BZX84J-B22	BZX84J-B75	BZX84J-C43
BZX84C68LT1G	BZX84J-B24	BZX84J-B7V5	BZX84J-C47
BZX84-C6V2	BZX84J-B27	BZX84J-B8V2	BZX84J-C4V3
BZX84C6V2LT1G	BZX84J-B2V4	BZX84J-B9V1	BZX84J-C4V7
BZX84C6V2LT3G	BZX84J-B2V7	BZX84J-C10	BZX84J-C51
BZX84-C6V8	BZX84J-B30	BZX84J-C11	BZX84J-C56
BZX84C6V8LT1G	BZX84J-B33	BZX84J-C12	BZX84J-C5V1
BZX84C6V8LT3G	BZX84J-B36	BZX84J-C13	BZX84J-C5V6
BZX84-C75	BZX84J-B39	BZX84J-C15	BZX84J-C62
BZX84C75LT1G	BZX84J-B3V0	BZX84J-C16	BZX84J-C68
BZX84-C7V5	BZX84J-B3V3	BZX84J-C18	BZX84J-C6V2
BZX84C7V5LT1G	BZX84J-B3V6	BZX84J-C20	BZX84J-C6V8

Multisim 14.0 Base Components

BZX84J-C75	BZX85-C4V3	BZX884-B24	BZX884-B7V5
BZX84J-C7V5	BZX85-C4V7	BZX884-B27	BZX884-B8V2
BZX84J-C8V2	BZX85-C51	BZX884-B2V4	BZX884-B9V1
BZX84J-C9V1	BZX85-C56	BZX884-B2V7	BZX884-C10
BZX85-C10	BZX85-C5V1	BZX884-B30	BZX884-C11
BZX85-C100	BZX85-C5V6	BZX884-B33	BZX884-C12
BZX85-C11	BZX85-C62	BZX884-B36	BZX884-C13
BZX85-C12	BZX85-C68	BZX884-B39	BZX884-C16
BZX85-C13	BZX85-C6V2	BZX884-B3V0	BZX884-C20
BZX85-C15	BZX85-C6V8	BZX884-B3V3	BZX884-C22
BZX85-C16	BZX85-C75	BZX884-B3V6	BZX884-C24
BZX85-C18	BZX85-C7V5	BZX884-B3V9	BZX884-C2V4
BZX85-C20	BZX85-C82	BZX884-B43	BZX884-C2V7
BZX85-C22	BZX85-C8V2	BZX884-B47	BZX884-C30
BZX85-C24	BZX85-C91	BZX884-B4V3	BZX884-C33
BZX85-C27	BZX85-C9V1	BZX884-B4V7	BZX884-C36
BZX85-C30	BZX884-B10	BZX884-B51	BZX884-C3V0
BZX85-C33	BZX884-B11	BZX884-B56	BZX884-C3V3
BZX85-C36	BZX884-B12	BZX884-B5V1	BZX884-C3V6
BZX85-C39	BZX884-B13	BZX884-B5V6	BZX884-C3V9
BZX85-C3V3	BZX884-B15	BZX884-B62	BZX884-C43
BZX85-C3V6	BZX884-B16	BZX884-B68	BZX884-C47
BZX85-C3V9	BZX884-B18	BZX884-B6V2	BZX884-C4V3
BZX85-C43	BZX884-B20	BZX884-B6V8	BZX884-C4V7
BZX85-C47	BZX884-B22	BZX884-B75	BZX884-C51

Multisim 14.0 Base Components

BZX884-C56	CA0158T	CA3060E	CA3130E
BZX884-C5V1	CA0224E	CA3078AE	CA3130M
BZX884-C62	CA0224M	CA3078AM	CA3130T
BZX884-C68	CA0258AE	CA3078AT	CA3140E
BZX884-C6V2	CA0258AM	CA3078E	CA3140M
BZX884-C75	CA0258AT	CA3078M	CA3140T
BZX884-C7V5	CA0258E	CA3078T	CA3160E
BZX884-C8V2	CA0258M	CA3080	CA3160T
BZX884-C9V1	CA0258T	CA3080A	CA3193AE
C232A	CA0324E	CA3080AE	CA3193AT
C232B	CA0324M	CA3080AM	CA3193E
C232D	CA0358AE	CA3080E	CA3193T
C232F	CA0358AM	CA3080M	CA3240AE
C232M	CA0358AT	CA3094AE	CA3240AE1
C233A	CA0358E	CA3094AM	CA3240E
C233B	CA0358M	CA3094AT	CA3240E1
C233D	CA0358T	CA3094BE	CA3260E
C233F	CA0741E	CA3094BM	CA3260T
C233M	CA0741T	CA3094BT	CA3280E
CA0124E	CA1458E	CA3094E	CA3440AE
CA0124M	CA1458T	CA3094M	CA3440M
CA0158AE	CA2902M	CA3094T	CA3450E
CA0158AT	CA2902N	CA3100E	CA5130AE
CA0158E	CA2904E	CA3100M	CA5130AM
CA0158M	CA2904M	CA3100T	CA5130AT

Multisim 14.0 Base Components

CA5130E	CLC200AK	CLC404AJM5	CLC411AJP
CA5130M	CLC200AM	CLC404AJP	CLC412A8B
CA5130T	CLC201	CLC405A8B	CLC412AIB
CA5160AE	CLC203	CLC405AIB	CLC412AJE
CA5160AM	CLC220	CLC405AJE	CLC412AJP
CA5260AE	CLC400A8B	CLC405AJP	CLC414A8B
CA5260AM	CLC400A8D	CLC406A8B	CLC414A8D
CA5260E	CLC400AIB	CLC406A8D	CLC414AJE
CA5260M	CLC400AID	CLC406AJE	CLC414AJP
CA5420E	CLC400AJE	CLC406AJM5	CLC415A8B
CA5420M	CLC400AJP	CLC406AJP	CLC415A8D
CA5420T	CLC401A8B	CLC407AIB	CLC415AJE
CA5470E	CLC401A8D	CLC407AJE	CLC415AJP
CA5470M	CLC401AIB	CLC407AJP	CLC416AJE
CAP_ELECTROLIT_VIRTUAL	CLC401AID	CLC409A8D	CLC416AJP
	CLC401AJE	CLC409AID	CLC417AJE
CAPACITOR_VIRTUAL	CLC401AJP	CLC409AJE	CLC417AJP
	CLC402A8B	CLC409AJM5	CLC420A8B
CHIRP_CURRENT	CLC402A8D	CLC409AJP	CLC420A8D
CLC103AI	CLC402AID	CLC410A8B	CLC420AIB
	CLC402AJE	CLC410A8D	CLC420AJE
CLC103AM	CLC402AJP	CLC410AJE	CLC420AJP
CLC111AJE	CLC404A8D	CLC410AJP	CLC420B8B
CLC111AJP	CLC404AID	CLC411A8B	CLC420B8D
CLC200A8C	CLC404AJE	CLC411AJE	CLC420BIB
CLC200AI			

Multisim 14.0 Base Components

CLC420BJE	CLC440AJE	CNTR_4BIN_SU_D	CONTROL_1C
CLC420BJP	CLC440AJP	CNTR_4BINS_DC	CONTROL_2A
CLC423AJE	CLC449A8B	CNTR_4SBIN	CONTROL_2C
CLC423AJP	CLC449AJE	CNTR_4SDEC	CONTROL_3A
CLC425A8B	CLC449AJP	CNTR_7BIN	CONTROL_3C
CLC425AIB	CLC501A8D	CNTR_8SBIN	CONTROL_4A
CLC425AJE	CLC501AID	CNTR_BCD_S	CONTROL_4C
CLC425AJP	CLC501AJE	CNTR_BCD_SDC	CONTROL_NC
CLC426A8B	CLC501AJP	CNTR_BCD_SU_D	CONTROL_NO
CLC426AIB	CLC502A8D	CNTR_BIN_DEC_SU_D	CONTROLLED_ONE_SHOT
CLC426AJE	CLC502AID	CNTR_JOHNSON	COP87L20CJN
CLC426AJP	CLC502AJE	CNY17F-3	COP87L22CJN
CLC428A8B	CLC502AJP	CNY17F-3X001	COP87L40CJN
CLC428AJE	CLC505A8D	CNY17F-3X006	COP87L40RJN
CLC428AJP	CLC505AJE	CNY17F-3X007T	COP87L42CJN
CLC430A8B	CLC505AJP	CNY17F-3X009T	COP87L42RJN
CLC430AJE	CLOCK_CURRENT	CNY17F-3X016	CORELESS_COIL_VIRTUAL
CLC430AJP	CLOCK_VOLTAGE	CNY17F-3X017	COUNT_OFF
CLC431A8B	CM1213A-02SR	CNY17F-3X019	COUNT_OFF_HOLD
CLC431AJE	CNTR_16SBIN	COMP_4	COUNT_OFF_RESET
CLC431AJP	CNTR_4ABIN	COMPARATOR_IDEAL	COUNT_ON
CLC432A8B	CNTR_4ADEC	COMPARATOR_VIRTUAL	COUNT_ON_HOLD
CLC432AJE	CNTR_4BIN_AS	CONTROL_1A	COUNT_ON_RESET
CLC432AJP	CNTR_4BIN_ASCLR		
CLC440A8B	CNTR_4BIN_S		

Multisim 14.0 Base Components

COUNT_UPDOWN_O FF	CURRENT_CONTROLLED_SPST_ANIMATED	D1N4148	DCD_2TO4
COUNT_UPDOWN_N	CURRENT_CONTROLLED_VOLTAGE_SOURCE	D44C12G	DCD_3TO8
COUPLED_INDUCTORS	CURRENT_LIMITER_BLOCK	D44H11G	DCD_4TO16
CPH3105-TL-E	CY37032P44-125AC	D44H8G	DCD_7SEG
CPH3123-TL-E	CY37032P44-125AI	D44VH10G	DCD_7SEG_P
CPH3144-TL-E	CY37032P44-125JC	D45C12G	DCD_BARGRAPH
CPH3205-TL-E	CY37032P44-125JI	D45H11G	DCD_HEX
CPH3223-TL-E	CY37032P44-154AC	D45H8G	DCD_HEX_BLUE
CPH3448-TL-H	CY37032P44-154AI	D45VH10G	DCD_HEX_DIG_BLUE
CPH5505-TL-E	CY37032P44-154JC	DAC7642_FP32	DCD_HEX_DIG_GREEN
CPH5506-TL-E	CY37032P44-154JI	DAC7643_FP32	DCD_HEX_DIG_ORANGE
CPH6223-TL-E	CY37032P44-200AC	DAC8541	DCD_HEX_DIG_ORANGE
CPH6341-TL-E	CY37032P44-200JC	DAN222M3T5G	DCD_HEX_DIG_RED
CPH6445-TL-E	CY37032P44-222AC	DAP222M3T5G	DCD_HEX_DIG_YELLOW
CPH6531-TL-E	CY37032P44-222JC	DBREAK	DCD_HEX_GREEN
CRYSTAL_VIRTUAL	CYPRESS-ULTRA-ISR-HDR	DC_CURRENT	DCD_HEX_ORANGE
CS494001-LQFP(144)	D_FF	DC_INTERACTIVE_CURRENT	DCD_HEX_YELLOW
CS494501-TQFP(100)	D_FF_NEGSR	DC_INTERACTIVE_VOLTAGE	DEC_BCD_10_INV
CURRENT_CONTROLLED_CURRENT_SOURCE	D_FF_POSSR	DC_MACHINE_PERMANENT_MAGNET	DEC_BCD_7
CURRENT_CONTROLLED_SPST	D_LATCH	DC_MACHINE_WOUND_FIELD	DEC2_4
	D_LATCH_NEGSR	DC_POWER	DEC3_8
		DCC010-TB-E	DEC4_10
			DELAY

Multisim 14.0 Base Components

DEM4_16	DIP18	DPST_2NC_DB	DSUB37F
DF06MA-E3/45	DIP20	DPST_2NC_SB	DSUB37M
DF10S/45	DIP22	DPST_2NO_DB	DSUB9F
DF10SA-E3/45	DIP24	DPST_2NO_SB	DSUB9M
DF1510S-E3/77	DIP28	DS1846_SO20	DSWPK_10
DF3A6.8FUT1G	DIP4	DS80C310_LCC44	DSWPK_2
DF6A6.8FUT1G	DIP6	DS80C320_LCC44	DSWPK_3
DGND	DIP8	DS80C323_LCC44	DSWPK_4
DIGITAL_CLOCK	DIPSW1	DS83C520_LCC44	DSWPK_5
DIGITAL_CONSTANT	DIPSW10	DS83C530_FP52	DSWPK_6
	DIPSW2	DS87C520_LCC44	DSWPK_7
DIGITAL_FREQUENCY_DIVIDER	DIPSW3	DS87C530_FP52	DSWPK_8
DIGITAL_HIGH	DIPSW4	DSP16210-TQFP(144)	DSWPK_9
DIGITAL_LOW	DIPSW5		DTA113EET1G
DIGITAL_PULLDOWN	DIPSW6	DSP1628-BQFP(100)	DTA113EM3T5G
	DIPSW7	DSP1628-TQFP(100)	DTA114EET1G
DIGITAL_PULLUP	DIPSW8		DTA114EM3T5G
DIGITAL_STATE_MACHINE	DIPSW9	DSP16410B-PBGA(208)	DTA114TET1G
DIODE	DIV		DTA114TM3T5G
	DIVIDER	DSUB15F	DTA114YET1G
DIODE		DSUB15F-VGA	
DIP10	DP8421A	DSUB15M	DTA114YM3T5G
	DP8421A_LCC68		DTA115EET1G
DIP12		DSUB15M-VGA	
	DP8422A_LCC84		DTA115EM3T5G
DIP14		DSUB25F	
	DPDT_DB		DTA115TET1G
DIP16		DSUB25M	
	DPDT_SB		DTA115TM3T5G

Multisim 14.0 Base Components

DTA123EM3T5G	DTC115TM3T5G	ECH8649-TL-H	EL2022/EL
DTA123TET1G	DTC123EM3T5G	ECH8651R-R-TL-H	EL2022CG
DTA123TM3T5G	DTC123JET1G	ECH8651R-TL-H	EL2022G
DTA124EET1G	DTC123JM3T5G	ECH8652-TL-H	EL2157CN
DTA124EM3T5G	DTC123TET1G	ECH8653-TL-H	EL2157CS
DTA124XM3T5G	DTC123TM3T5G	ECH8654-TL-H	EL2210CN
DTA143EET1G	DTC124EET1G	ECH8657-TL-H	EL2210CS
DTA143EM3T5G	DTC124EM3T5G	ECH8660-TL-H	EL2211CN
DTA143ZET1G	DTC124XET1G	ECH8662-TL-H	EL2211CS
DTA143ZM3T5G	DTC124XM3T5G	EDF1DS-E3/45	EL2310CN
DTA144EET1G	DTC143EET1G	EDR201A05	EL2310CS
DTA144EM3T5G	DTC143EM3T5G	EDR201A12	EL2311CN
DTA144TET1G	DTC143TM3T5G	EDR201A24	EL2311CS
DTA144TM3T5G	DTC143ZET1G	EDR2H1A05	EL2410CN
DTA144WM3T5G	DTC143ZM3T5G	EDR2H1A12	EL2410CS
DTC113EET1G	DTC144EET1G	EDR2H1A24	EL2411CN
DTC113EM3T5G	DTC144EM3T5G	EGF1D-E3/67A	EL2411CS
DTC114EET1G	DTC144TET1G	EGF1T-E3/67A	EL2500/EL
DTC114EM3T5G	DTC144TM3T5G	EGP10D-E3/54	EL2520/EL
DTC114TET1G	DTC144WM3T5G	EGP10G-E3/54	EL2600/EL
DTC114TM3T5G	ECG6407	EGP50D-E3/54	EL2620/EL
DTC114YET1G	ECG6408	EGP50G-E3/54	EL4089CN
DTC115EET1G	ECG6411	EL2006CG	EL4089CS
DTC115EM3T5G	ECG6412	EL2006G	EL4430CN
DTC115TET1G	ECH8102-TL-H	EL2006G/883B	EL4430CS

Multisim 14.0 Base Components

EL4451CN	EMR011B12	EMR031B06	EMR131A24
EL4451CS	EMR011B24	EMR031B08	EMR131B03
EL4452CN	EMR021A03	EMR031B09	EMR131B05
EL4452CS	EMR021A05	EMR031B12	EMR131B06
ELH0032G/883B	EMR021A06	EMR031B24	EMR131B08
ELH0101K/883B	EMR021A08	EMR121A03	EMR131B09
EMC2DXV5T1G	EMR021A09	EMR121A05	EMR131B12
EMC3DXV5T1G	EMR021A12	EMR121A06	EMR131B24
EMC3DXV5T5G	EMR021A24	EMR121A08	EMR151A03
EMC4DXV5T1G	EMR021B03	EMR121A09	EMR151A05
EMC5DXV5T1G	EMR021B05	EMR121A12	EMR151A06
EMH1303-TL-E	EMR021B06	EMR121A24	EMR151A08
EMH1405-TL-H	EMR021B08	EMR121B03	EMR151A09
EMR011A03	EMR021B09	EMR121B05	EMR151A12
EMR011A05	EMR021B12	EMR121B06	EMR151A24
EMR011A06	EMR021B24	EMR121B08	EMR161A03
EMR011A08	EMR031A03	EMR121B09	EMR161A05
EMR011A09	EMR031A05	EMR121B12	EMR161A06
EMR011A12	EMR031A06	EMR121B24	EMR161A08
EMR011A24	EMR031A08	EMR131A03	EMR161A09
EMR011B03	EMR031A09	EMR131A05	EMR161A12
EMR011B05	EMR031A12	EMR131A06	EMR171A03
EMR011B06	EMR031A24	EMR131A08	EMR171A05
EMR011B08	EMR031B03	EMR131A09	EMR171A06
EMR011B09	EMR031B05	EMR131A12	EMR171A08

Multisim 14.0 Base Components

EMR171A09	EPM7032-TQFP(44)	EPM7128A-TQFP(144)	ESD5Z5.0T1G
EMR171A12	EPM7064-PLCC(44)		ESD5Z6.0T1G
EMR171A24	EPM7064-PLCC(68)	EPM7512AE-PQFP(208)	ESD5Z7.0T1G
EMX1DXV6T1G	EPM7064-PLCC(84)	EPM7512AE-TQFP(144)	ESD5Z7.0T5G
EMX1DXV6T5G	EPM7064-PQFP(100)		ESD7004MUTAG
EN2016CM		ES1B-E3/61T	ESD7008MUTAG
EN2016CN	EPM7064S-PLCC(44)	ES1C-E3/61T	ESD7016MUTAG
ENC_10TO4	EPM7064S-PLCC(84)	ES1D-E3/61T	ESD7104MUTAG
ENC_8TO3		ES1PD-E3/84A	ESD7951ST5G
ENC_8TO3S	EPM7064S-TQFP(100)	ES2B-E3/52T	ESD7C3.3DT5G
ENC10_4	EPM7064S-TQFP(44)	ES2C-E3/52T	ESD7C5.0DT5G
ENC8_3		ES2D-E3/52T	ESD8004MUTAG
ENERGIZING_COIL	EPM7064-TQFP(44)	ES3D-E3/57T	ESD8040MUTAG
ENERGIZING_COIL_AC	EPM7096-PLCC(68)	ESD0P2RF-02LRH	ESD8V0R1B-02EL
	EPM7096-PLCC(84)	ESD0P2RF-02LS	ESD8V0R1B-02ELS
ENERGIZING_COIL_TIMED	EPM7096-PQFP(100)	ESD11L5.0DT5G	ESD9B3.3ST5G
EP2015ACN		ESD18VU1B-02LRH	ESD9B5.0ST5G
EP2015CM	EPM7128AE-PLCC(84)	ESD18VU1B-02LS	ESD9C3.3ST5G
EP2015CN	EPM7128AE-TQFP(100)	ESD3V3U4ULC	ESD9C5.0ST5G
EPM7032-PLCC(44)		ESD5B5.0ST1G	ESD9L5.0ST5G
EPM7032-PQFP(44)	EPM7128AE-TQFP(144)	ESD5V3L1B-02LS	ESD9X12ST5G
		ESD5V3U4U-HDMI	ESD9X3.3ST5G
EPM7032S-PLCC(44)	EPM7128A-PLCC(84)	ESD5Z12T1G	ESD9X5.0ST5G
EPM7032S-TQFP(44)	EPM7128A-TQFP(100)	ESD5Z2.5T1G	ESDR0502NMUTAG
		ESD5Z3.3T1G	ESDR0502NMUTBG

Multisim 14.0 Base Components

ESDR0544MDMR4G	FEP30JPE3/45	FMMT489	FMMV2102
ESH1PD-E3/84A	FES16BT-E3/45	FMMT491A	FMMV2103
EVAL-SDP-CB1Z	FES16GT-E3/45	FMMT5179	FMMV2104
EVAL-SDP-CH1Z	FES8DT-E3/45	FMMT549	FMMV2105
EVAL-SDP-CH1Z_FMC	FF_D_CO	FMMT589	FMMV2106
EVAL-SDP-CS1Z	FF_D_PCLR_CO	FMMT591A	FMMV2107
EXPONENTIAL_CURRENT	FF_D4_CLR_CO	FMMT597	FMMV2108
EXPONENTIAL_VOLTAGE	FF_JK_NSCLR_CO	FMMT597Q	FMMV2109
	FF_JK_PSCLR_CO	FMMT617	FMMV3102
	FF_T_CLR_CO	FMMT618	FOOT_NC
F1007	FLOAT_NC	FMMT619	FOOT_NO
F1008	FLOAT_NO	FMMT624	FREQ_DIVIDER
F1020	FLOW_NC	FMMT625	FREQUENCY_TABLE_FUNCTION
FAST_1A	FLOW_NO	FMMT717	FSK_VOLTAGE
FAST_2A	FM_CURRENT	FMMT718	FULL_ADDER
FAST_3A	FM_VOLTAGE	FMMT720	FUSE
FAST_4A	FMMD2835	FMMT722	FUSE_VIRTUAL
FCN-268D024-G/10-R	FMMD2836	FMMT723	FX2-100S-1.27DS(71)
FCX458	FMMD2837	FMMT918	FX8-120P-SV1(91)
FCX558	FMMD2838	FMMTA20	FX8-120S-SV(21)
FCX649	FMMD6050	FMMTA70	FZT604
FCX749	FMMD6100	FMMTH10	FZT605
FEP16DT-E3/45	FMMD7000	FMMV105G	FZT649
FEP30GP-E3/45	FMMD914	FMMV109	FZT651
	FMMT38B	FMMV2101	

Multisim 14.0 Base Components

FZT657	GBU6G-E3/45	GL34D	GLL4756
FZT658	GBU6M-E3/45	GL34G	GLL4757
FZT688B	GEN_CNTR_4ABIN	GL34G-E3/98	GLL4758
FZT689B	GF1A	GL34J	GLL4759
FZT690B	GF1B	GLL4735	GLL4760
FZT692B	GF1D	GLL4736	GLL4761
FZT694B	GF1G	GLL4737	GLL4762
FZT696B	GF1G-E3/67A	GLL4738	GLL4763
FZT705	GF1J	GLL4739	GP02-20
FZT749	GF1K	GLL4740	GP02-25
FZT751	GF1M	GLL4741	GP02-30
FZT757	GI250-1	GLL4742	GP02-35
FZT758	GI250-2	GLL4743	GP02-40
FZT788A	GI250-3	GLL4744	GP08A
FZT788B	GI250-4	GLL4745	GP08B
FZT789A	GI751-E3/54	GLL4746	GP08D
FZT790A	GI810	GLL4747	GP08G
FZT792A	GI811	GLL4748	GP08J
G3SBA60-E3/51	GI812	GLL4749	GP10A
GaAsFET_N	GI814	GLL4750	GP10B
GaAsFET_P	GI816	GLL4751	GP10D
GAIN_2_PIN	GI817	GLL4752	GP10G
GBPC3506W-E4/51	GI818	GLL4753	GP10J
GBU4G-E3/45	GL34A	GLL4754	GP10K
GBU4M-E3/51	GL34B	GLL4755	GP10M

Multisim 14.0 Base Components

GP10N	GP30M	HA1-4741-2	HA2-2548-9
GP10Q	GROUND	HA1-4741-5	HA2-2600-2
GP10T	GROUND_REF1	HA1-5104-2	HA2-2602-2
GP10V	GROUND_REF2	HA1-5104-5	HA2-2605-5
GP10W	GROUND_REF3	HA1-5114-2	HA2-2620-2
GP10Y	GROUND_REF4	HA1-5114-5	HA2-2622-2
GP10Y-E3/54	GROUND_REF5	HA1-5134-2	HA2-2625-5
GP15A	GSB311A41EU	HA1-5134-5	HA2-2640-2
GP15B	GSB3211311WEU	HA1-5190-2	HA2-5101-2
GP15D	GSIB1580-E3/45	HA2-2500-2	HA2-5102-2
GP15G	GSIB2560-E3/45	HA2-2502-2	HA2-5102-5
GP15J	GTO	HA2-2510-2	HA2-5130-5
GP15K	HA1-2539-2	HA2-2512-2	HA2-5135-5
GP15M	HA1-2539-5	HA2-2515-2	HA2-5142-2
GP20A	HA1-2540-2	HA2-2520-2	HA2-5142-5
GP20B	HA1-2540-5	HA2-2522-2	HA2-5147-2
GP20D	HA1-2541-2	HA2-2525-5	HA2-5147-5
GP20G	HA1-2541-5	HA2-2529-2	HA2-5160-2
GP20J	HA1-2542-2	HA2-2529-5	HA2-5160-5
GP30A	HA1-2542-5	HA2-2541-2	HA2-5162-5
GP30B	HA1-2839-5	HA2-2541-5	HA2-5170-2
GP30D	HA1-2840-5	HA2-2542-2	HA2-5170-5
GP30G	HA1-2840-9	HA2-2542-5	HA2-5190-2
GP30J	HA1-2850-5	HA2-2544-2	HA2-5221-5
GP30K	HA1-2850-9	HA2-2548-5	HA2-7712A-5

Multisim 14.0 Base Components

HA2-7712A-9	HA3-2850-9	HA3B2842-5	HA7-2840-9
HA2-7712B-5	HA3-4741-5	HA3B2842-9	HA7-2850-5
HA2-7712B-9	HA3-5101-5	HA3B2850-5	HA7-2850-9
HA3-2444-5	HA3-5102-5	HA3B2850-9	HA7-5101-2
HA3-2444-9	HA3-5104-5	HA4P2525-5	HA7-5102-2
HA3-2525-5	HA3-5111-5	HA7-2500-2	HA7-5102-5
HA3-2529-5	HA3-5112-5	HA7-2510-2	HA7-5111-2
HA3-2539-5	HA3-5114-5	HA7-2512-2	HA7-5112-2
HA3-2539C-5	HA3-5127-5	HA7-2515-2	HA7-5127-2
HA3-2540-5	HA3-5127A-5	HA7-2520-2	HA7-5127-5
HA3-2542-5	HA3-5142-5	HA7-2522-2	HA7-5127A-2
HA3-2544-5	HA3-5147-5	HA7-2525-5	HA7-5127A-5
HA3-2544C-5	HA3-5177-5	HA7-2529-5	HA7-5130-2
HA3-2548-5	HA3-5221-5	HA7-2544-2	HA7-5130-5
HA3-2605-5	HA3-5222-5	HA7-2544-5	HA7-5135-2
HA3-2625-5	HA3-5232-5	HA7-2548-5	HA7-5135-5
HA3-2839-5	HA3-5232-9	HA7-2600-2	HA7-5137-2
HA3-2839-9	HA3-7712A-5	HA7-2602-2	HA7-5137-5
HA3-2840-5	HA3-7712A-9	HA7-2605-5	HA7-5142-2
HA3-2840-9	HA3-7712B-5	HA7-2620-2	HA7-5142-5
HA3-2841-5	HA3-7712B-9	HA7-2622-2	HA7-5147-2
HA3-2841-9	HA3B2840-5	HA7-2625-5	HA7-5147-5
HA3-2842-5	HA3B2840-9	HA7-2640-2	HA7-5170-2
HA3-2842-9	HA3B2841-5	HA7-2645-5	HA7-5170-5
HA3-2850-5	HA3B2841-9	HA7-2840-5	HA7-5177-5

Multisim 14.0 Base Components

HA7-5221-5	HA9P4741-9	HC-49/U_11MHz	HCNW3120-300E
HA7-5221-9	HA9P5101-5	HC-49/U_15MHz	HCPL-0201-000E
HA7-5222-5	HA9P5101-9	HC-49/U_25MHz	HCPL-0201-060E
HA7-5222-9	HA9P5102-5	HC-49/U_3MHz	HCPL-0211-000E
HA9P2444-5	HA9P5102-9	HC-49/U_40MHz	HCPL-0211-060E
HA9P2444-9	HA9P5104-5	HC-49/U_5MHz	HCPL-0302-000E
HA9P2529-5	HA9P5104-9	HC-49/U_7MHz	HCPL-0302-060E
HA9P2539-5	HA9P5111-5	HC-49/U_80MHz	HCPL-0314-000E
HA9P2539-9	HA9P5111-9	HC-49/US_11MHz	HCPL-0314-060E
HA9P2540-5	HA9P5112-5	HC-49/US_15MHz	HCPL-0454-000E
HA9P2544-5	HA9P5112-9	HC-49/US_25MHz	HCPL-0454-060E
HA9P2544-9	HA9P5114-5	HC-49/US_40MHz	HCPL-0466-000E
HA9P2544C-5	HA9P5114-9	HC-49/US_5MHz	HCPL-0466-060E
HA9P2544C-9	HA9P5127-5	HC-49/US_7MHz	HCPL-0501-500E
HA9P2548-5	HA9P5137-5	HCNR200-000E	HCPL-0501-560E
HA9P2605-5	HA9P5142-9	HCNR200-050E	HCPL-063L-000E
HA9P2625-5	HA9P5221-5	HCNR200-300E	HCPL-063L-060E
HA9P2840-5	HA9P5222-5	HCNR200-350E	HCPL-0701-000E
HA9P2840-9	HA9P5222-9	HCNW136-000E	HCPL-0701-060E
HA9P2841-5	HA9P5232-5	HCNW136-300E	HCPL-181-000E
HA9P2841-9	HA9P5232-9	HCNW139-000E	HCPL-181-060E
HA9P2842-5	HA9P7712B-5	HCNW139-300E	HCPL-2200-000E
HA9P2842-9	HA9P7712B-9	HCNW2201-000E	HCPL-2200-300E
HA9P2850-5	HALF_ADDER	HCNW2201-300E	HCPL-2201-000E
HA9P2850-9	HC-49/U_1.5MHz	HCNW3120-000E	HCPL-2201-060E

Multisim 14.0 Base Components

HCPL-2201-300E	HCPL-263L-300E	HCPL-4506-320E	HDR1X23
HCPL-2201-360E	HCPL-263L-320E	HCPL-4506-360E	HDR1X24
HCPL-2202-000E	HCPL-263L-560E	HCPL-7800-000E	HDR1X25
HCPL-2202-060E	HCPL-3020-000E	HCPL-7800-300E	HDR1X3
HCPL-2202-300E	HCPL-3020-060E	HCPL-J312-000E	HDR1X4
HCPL-2202-360E	HCPL-3020-300E	HCPL-J312-300E	HDR1X5
HCPL-2211-000E	HCPL-3120-000E	HD4A	HDR1X6
HCPL-2211-060E	HCPL-3120-060E	HD64F2134FA20	HDR1X7
HCPL-2211-300E	HCPL-3120-300E	HD64F2134TF20	HDR1X8
HCPL-2211-360E	HCPL-3120-360E	HD64F2134VFA10	HDR1X9
HCPL-2212-000E	HCPL-3140-000E	HD64F2134VTF10	HDR2X10
HCPL-2212-060E	HCPL-3140-060E	HDR1X10	HDR2X11
HCPL-2212-300E	HCPL-3140-300E	HDR1X11	HDR2X12
HCPL-2212-360E	HCPL-3140-360E	HDR1X12	HDR2X13
HCPL-2219-000E	HCPL-316J-000E	HDR1X13	HDR2X14
HCPL-2219-060E	HCPL-4504-000E	HDR1X14	HDR2X15
HCPL-2219-300E	HCPL-4504-020E	HDR1X15	HDR2X16
HCPL-2219-360E	HCPL-4504-060E	HDR1X16	HDR2X17
HCPL-2231-000E	HCPL-4504-300E	HDR1X17	HDR2X18
HCPL-2231-300E	HCPL-4504-320E	HDR1X18	HDR2X19
HCPL-2232-000E	HCPL-4504-360E	HDR1X19	HDR2X2
HCPL-2232-300E	HCPL-4506-000E	HDR1X2	HDR2X20
HCPL-263L-000E	HCPL-4506-020E	HDR1X20	HDR2X21
HCPL-263L-020E	HCPL-4506-060E	HDR1X21	HDR2X22
HCPL-263L-060E	HCPL-4506-300E	HDR1X22	HDR2X23

Multisim 14.0 Base Components

HDR2X24	HFA7-0002-9	HSP45240GM-40/883	ICM7555MJA
HDR2X25	HFA7-0005-5		ICM7555MTV
HDR2X3	HFA7-0005-9	ICL7611ACPA	ICM7556IPD+
HDR2X4	HFA9P0001-5	ICL7611ACTV	ICM7556ISD+
HDR2X5	HFA9P0002-5	ICL7611AMTV	ICM7556MJD+
HDR2X6	HFA9P0002-9	ICL7611DCBA	IDAC
HDR2X7	HFA9P0005-5	ICL7650SCBA-1	IDAC16
HDR2X8	HFA9P0005-9	ICL7650SCBD	IDT7210L20C
HDR2X9	HMA510GM-55/833	ICL7650SCPA	IDT7210L20F
HELD_CLOSED_LIMIT	HMA510GM-65/833	ICL7650SCPD	IDT7210L20G
HELD_OPEN_LIMIT	HMA510GM-75/833	ICL7650SCTV-1	IDT7210L20J
HFA1-0001-5	HSDL-5400	ICL7650SIJD	IDT7210L25C
HFA1-0001-9	HSDL-5420	ICL7650SIPA-1	IDT7210L25F
HFA2-0002-5	HSDL-5420#031	ICL7650SIPD	IDT7210L25G
HFA2-0002-9	HSP43124PC-33	ICL7650SITV-1	IDT7210L25J
HFA2-0005-5	HSP43124PC-45	ICL7650SMJD	IDT7210L35C
HFA2-0005-9	HSP43168GM-25/883	ICL7650SMTV-1	IDT7210L35F
HFA3-0001-5	HSP45240GM-25/883	ICL7652	IDT7210L35G
HFA3-0001-9	HSP43168GM-33/883	ICL7652D	IDT7210L35J
HFA3-0002-5	HSP45240GM-25/883	ICL7652P	IDT7210L45C
HFA3-0002-9	HSP43168GM-33/883	ICM7555ESA+	IDT7210L45F
HFA3-0005-5	HSP45240GM-25/883	ICM7555IJA+	IDT7210L45G
HFA3-0005-9	HSP45240GM-33/883	ICM7555IPA+	IDT7210L45J
HFA7-0002-5		ICM7555ISA+	IDT7210L55C
		ICM7555ITV	IDT7210L55F

Multisim 14.0 Base Components

IDT7210L55G	INA169NA	INA213AIRSWR	INDUCTOR_ADVANCED
IDT7210L55J	INA170EA	INA213BIDCKR	Inductor_Lossy
IDT7210L65C	INA193AID	INA213BIRSWR	INDUCTOR_VIRTUAL
IDT7210L65F	INA194AID	INA214AIDCKR	
IDT7210L65G	INA195AID	INA214AIRSWR	INTERACTIVE_DIGITAL_CONSTANT
IDT7210L65J	INA201AID	INA214BIDCKR	
ILLUMINATED_PB	INA201AIDGKR	INA214BIRSWR	INV
IMSA110-G20S	INA206AID	INA216A2RSWR	IPA028N08N3 G
INA105_CMP	INA206AIPW	INA216A2YFFR	IPA030N10N3 G
INA133U	INA210AIDCKR	INA216A3RSWR	IPA032N06N3 G
INA133UA	INA210AIRSWR	INA216A3YFFR	IPA037N08N3 G
INA138NA	INA210BIDCKR	INA216A4RSWR	IPA045N10N3 G
INA143U	INA210BIRSWR	INA216A4YFFR	IPA057N06N3 G
INA143UA	INA211AIDCKR	INA270AID	IPA057N08N3 G
INA145UA	INA211BIDCKR	INA271AID	IPA075N15N3 G
INA146UA	INA2126E/250	INA321E	IPA086N10N3 G
INA148UA	INA2126EA/250	INA321EA	IPA093N06N3 G
INA152EA/250	INA2126P	INA322EA	IPA100N08N3 G
INA154U	INA2126U	INA326EA	IPA105N15N3 G
INA154UA	INA212AIDCKR	INA327EA	IPA126N10N3 G
INA157U	INA212BIDCKR	INA331AIDGK	IPA180N10N3 G
INA157UA	INA2132U	INA331IDGK	IPB009N03L G
INA159AID	INA2132UA	INA332IDGK	IPB010N06N
INA163UA	INA213AIDCKR	INA333AIDGKR	IPB011N04L G
INA168NA	INA213AIDCKT	INA333AIDRGR	IPB011N04N G

Multisim 14.0 Base Components

IPB014N06N	IPB037N06N3 G	IPB093N04L G	IPD035N06L3 G
IPB015N04L G	IPB038N12N3 G	IPB096N03L G	IPD036N04L G
IPB015N04N G	IPB039N04L G	IPB097N08N3 G	IPD038N04N G
IPB016N06L3 G	IPB039N10N3 G	IPB107N20N3 G	IPD038N06N3 G
IPB017N06N3 G	IPB041N04N G	IPB107N20NA	IPD040N03L G
IPB019N06L3 G	IPB042N03L G	IPB108N15N3 G	IPD042P03L3 G
IPB019N08N3 G	IPB042N10N3 G	IPB114N03L G	IPD048N06L3 G
IPB020N04N G	IPB048N06L G	IPB123N10N3 G	IPD050N03L G
IPB020NE7N3 G	IPB049N06L3 G	IPB136N08N3 G	IPD053N06N
IPB021N06N3 G	IPB049NE7N3 G	IPB144N12N3 G	IPD053N06N3 G
IPB022N04L G	IPB050N06N G	IPB147N03L G	IPD053N08N3 G
IPB023N04N G	IPB052N04N G	IPB200N15N3 G	IPD060N03L G
IPB023N06N3 G	IPB054N06N3 G	IPB200N25N3 G	IPD068N10N3 G
IPB025N08N3 G	IPB054N08N3 G	IPB230N06L3 G	IPD068P03L3 G
IPB025N10N3 G	IPB055N03L G	IPB260N06N3 G	IPD075N03L G
IPB026N06N	IPB057N06N	IPB26CN10N G	IPD079N06L3 G
IPB027N10N3 G	IPB065N03L G	IPB320N20N3 G	IPD082N10N3 G
IPB029N06N3 G	IPB065N15N3 G	IPB34CN10N G	IPD088N04L G
IPB030N08N3 G	IPB067N08N3 G	IPB50CN10N G	IPD088N06N3 G
IPB031NE7N3 G	IPB072N15N3 G	IPB530N15N3 G	IPD090N03L G
IPB034N03L G	IPB075N04L G	IPB600N25N3 G	IPD096N08N3 G
IPB034N06L3 G	IPB080N03L G	IPD025N06N	IPD105N03L G
IPB034N06N3 G	IPB081N06L3 G	IPD031N03L G	IPD105N04L G
IPB035N08N3 G	IPB083N10N3 G	IPD031N06L3 G	IPD110N12N3 G
IPB036N12N3 G	IPB090N06N3 G	IPD034N06N3 G	IPD122N10N3 G

Multisim 14.0 Base Components

IPD127N06L G	IPI028N08N3 G	IPI180N10N3 G	IPP040N06N3 G
IPD12CN10N G	IPI029N06N	IPI200N15N3 G	IPP041N04N G
IPD135N03L G	IPI030N10N3 G	IPI200N25N3 G	IPP041N12N3 G
IPD135N08N3 G	IPI032N06N3 G	IPI26CN10N G	IPP042N03L G
IPD144N06N G	IPI034NE7N3 G	IPI320N20N3 G	IPP045N10N3 G
IPD160N04L G	IPI037N06L3 G	IPI35CN10N G	IPP048N12N3 G
IPD170N04N G	IPI037N08N3 G	IPI50CN10N G	IPP04CN10N G
IPD180N10N3 G	IPI040N06N3 G	IPI530N15N3 G	IPP052N06L3 G
IPD200N15N3 G	IPI041N12N3 G	IPI600N25N3 G	IPP052NE7N3 G
IPD220N06L3 G	IPI045N10N3 G	IPI80CN10N G	IPP055N03L G
IPD230N06N G	IPI04CN10N G	IPP015N04N G	IPP057N06N3 G
IPD250N06N3 G	IPI052NE7N3 G	IPP020N06N	IPP057N08N3 G
IPD25CN10N G	IPI057N08N3 G	IPP023N04N	IPP05CN10L G
IPD320N20N3 G	IPI070N08N3 G	IPP023N04N G	IPP05CN10N G
IPD33CN10N G	IPI072N10N3 G	IPP023NE7N3 G	IPP060N06N
IPD350N06L G	IPI075N15N3 G	IPP024N06N3 G	IPP062NE7N3 G
IPD400N06N G	IPI076N12N3 G	IPP028N08N3 G	IPP065N03L G
IPD530N15N3 G	IPI084N06L3 G	IPP029N06N	IPP06CN10L G
IPD600N25N3 G	IPI086N10N3 G	IPP030N10N3 G	IPP070N08N3 G
IPD640N06L G	IPI100N08N3 G	IPP032N06N3 G	IPP072N10N3 G
IPD78CN10N G	IPI110N20N3 G	IPP034N03L G	IPP075N15N3 G
IPD800N06N G	IPI111N15N3 G	IPP034NE7N3 G	IPP076N12N3 G
IPI020N06N	IPI126N10N3 G	IPP037N06L3 G	IPP080N03L G
IPI023NE7N3 G	IPI139N08N3 G	IPP037N08N3 G	IPP084N06L3 G
IPI024N06N3 G	IPI147N12N3 G	IPP040N06N	IPP085N06L G

Multisim 14.0 Base Components

IPP086N10N3 G	IPP50CN10N G	IRF3205	IRFE130
IPP08CN10L G	IPP530N15N3 G	IRF3205S	IRFF110
IPP093N06N3 G	IPP600N25N3 G	IRF3710	IRFG110
IPP096N03L G	IPP80CN10N G	IRF3710S	IRFI1010N
IPP100N08N3 G	IPS031N03L G	IRF510	IRFI3710
IPP110N20N3 G	IPS040N03L G	IRF520	IRFI520N
IPP110N20NA	IPS050N03L G	IRF520N	IRFI5210
IPP111N15N3 G	IPS060N03L G	IRF520NS	IRFI5305
IPP114N03L G	IPS075N03L G	IRF5210	IRFI530N
IPP114N12N3 G	IPS090N03L G	IRF5210S	IRFI540N
IPP120N06N G	IPS105N03L G	IRF5305	IRFI840G
IPP126N10N3 G	IPS110N12N3 G	IRF5305S	IRFI840GLC
IPP12CN10L G	IPS118N10N G	IRF530N	IRFIZ44N
IPP139N08N3 G	IPS12CN10L G	IRF530NS	IRFIZ46N
IPP147N03L G	IPS135N03L G	IRF540	IRFIZ48N
IPP147N12N3 G	IPT004N03L	IRF540N	IRFM140
IPP16CN10L G	IPT007N06N	IRF540NS	IRFM150
IPP16CN10N G	IPT020N10N3	IRF541	IRFM9140
IPP180N10N3 G	IPT059N15N3	IRF7201	IRFN054
IPP200N15N3 G	IPU135N08N3 G	IRF7403	IRFP044N
IPP200N25N3 G	IRF1010N	IRF7404	IRFP048N
IPP230N06L3 G	IRF1010NS	IRF7413	IRFP054N
IPP260N06N3 G	IRF1310	IRF830	IRFP064
IPP26CN10N G	IRF250	IRF840	IRFP064N
IPP320N20N3 G	IRF2505S	IRF9530	IRFP140N

Multisim 14.0 Base Components

IRFP2410	IRFZ46NS	IRGPC40K	IRL530N
IRFP244	IRFZ48N	IRGPC40UD2	IRL530NS
IRFP250	IRFZ48NS	IRGPC50K	IRL540
IRFP260	IRG4BC10U	IRGPC50M	IRLI2203G
IRFP264	IRG4BC10UD	IRGPH40K	IRLI2203N
IRFP3710	IRG4BC15UD	IRGPH50K	IRLI2505
IRFP5210	IRG4BC20U	IRGPH50M	IRLI2703
IRFPG40	IRG4BC40S	IRL2203	IRLI2910
IRFR110	IRG4BC40U	IRL2203NS	IRLI3103
IRFR1205	IRG4BC40W	IRL2203S	IRLI3303
IRFR120N	IRG4PC30U	IRL2505	IRLI3803
IRFR3910	IRG4RC10K	IRL2505S	IRLI530N
IRFR4105	IRG4RC10KD	IRL2703	IRLIZ24N
IRFU110	IRG4RC10U	IRL2703S	IRLIZ34N
IRFU1205	IRG4RC10UD	IRL2910	IRLL3303
IRFU120N	IRGBC20F	IRL2910S	IRLP150
IRFU2605	IRGBC20K	IRL3103	IRLP2203
IRFU3910	IRGBC20S	IRL3103S	IRLP2505
IRFU4105	IRGBC20U	IRL3303	IRLP3705
IRFZ24N	IRGBC30F	IRL3303S	IRLP3803
IRFZ24NS	IRGBC30K	IRL3705	IRLR024N
IRFZ34N	IRGBC30UD2	IRL3705N	IRLR2703
IRFZ44N	IRGLC60KD1	IRL3705NS	IRLR2705
IRFZ44NS	IRGPC20F	IRL3803	IRLR2905
IRFZ46N	IRGPC20U	IRL3803S	IRLR3103

Multisim 14.0 Base Components

IRLR3303	J2N5905	JAN2N4033	L6208_DIP24
IRLU024N	J2N5906	JANTX2N2907A	L6208_SO24
IRLU2703	J2N5907	JANTX2N3700	L6208P_SO36
IRLU2705	J2N5908	JANTX2N4029	L6234_DIP20
IRLU2905	J2N5909	JANTX2N4033	L6234P_SO20
IRLU3103	J2N5911	JANTXV2N2907A	L6375_DIP8
IRLU3303	J2N5912	JANTXV2N3700	L6375_SO20
IRLZ34N	J2N6483	JANTXV2N4029	L64210GC-15
IRLZ34NS	J2N6484	JANTXV2N4033	L64210GC-20
IRLZ44N	J2N6485	JFET_N	L64210JC-15
J108	J308	JFET_P	L64210JC-20
J109	J309	JK_FF	L64210NC-15
J110	J310	JK_FF_NEGSR	L64210NC-20
J111	J401	L6201_SO20	L64211GC-15
J112	J402	L6201P_SO20	L64211GC-20
J113	J403	L6202_DIP18	L64211NC-15
J174	J404	L6203_ZIP11	L64211NC-20
J175	J405	L6205_DIP20	L6911C_SO20
J176	J406	L6205_SO20	L6911D_SO20
J177	J410	L6206_DIP24	L6911E_SO20
J210	J411	L6206_SO24	LA_CARRY_GEN
J211	J412	L6206P_SO36	LA_CARRY_GEN
J212	JAN2N2907A	L6207_DIP24	LAMP
J2N5902	JAN2N3700	L6207_SO24	LAMP_VIRTUAL
J2N5904	JAN2N4029	L6207P_SO36	LATCH_D

Multisim 14.0 Base Components

LATCH_D2	LF155H	LF355AH	LF411CP
LATCH_D4_SR_OE	LF155H/883	LF355BM	LF411ID
LATCH_SR	LF156AH	LF355BN	LF411IP
LATTICE- ispDOWNLOAD- HDR	LF156AH/883	LF355H	LF411MH
	LF156H	LF355M	LF411MH/883
LATTICE- ispDOWNLOAD- USB-HDR	LF156H/883	LF355N	LF411MWG/883
	LF157AH/883	LF356AH	LF412ACH
	LF157H/883	LF356BM	LF412ACN
LC03-6R2G	LF255H	LF356BN	LF412AMH
LD102A	LF256H	LF356H	LF412CD
LD103A	LF257H	LF356M	LF412CH
LD106	LF347BD	LF356N	LF412CJG
LED	LF347BN	LF357AH	LF412CN
LED_blue	LF347D	LF357BN	LF412CP
LED_green	LF347M	LF357H	LF412MH
LED_ir	LF347N	LF357M	LF412MH/883
LED_orange	LF351D	LF357N	LF412MJ/883
LED_red	LF351M	LF400	LF441AMH
LED_yellow	LF351N	LF411ACH	LF441CD
LF13741H	LF351P	LF411ACN	LF441CH
LF147D/883	LF353D	LF411AMH	LF441CJ
LF147J	LF353H	LF411CD	LF441CM
LF147J/883	LF353M	LF411CH	LF441CN
LF155AH	LF353N	LF411CJG	LF441MH/883
LF155AH/883	LF353P	LF411CN	LF442ACN

Multisim 14.0 Base Components

LF442AMH	LH0022CH	LH4162	LM101AW/883
LF442CD	LH0024CH	LHV870LC/NOPB	LM101D
LF442CH	LH0024H	LIMIT_NC	LM101F
LF442CJ	LH0024H-MIL	LIMIT_NO	LM101F/883
LF442CM	LH0032CG	LINKSYS-WRT54G- HD	LM101H
LF442CN	LH0032G	LM101AD	LM101H/883
LF442MH	LH0032G/883	LM101AD/883	LM101J-14
LF442MH/883	LH0041CG	LM101AF	LM101J-14/883
LF444ACN	LH0041CJ	LM101AF/883	LM107J
LF444AMD	LH0041G	LM101AFK	LM107JG
LF444CD	LH0042CH	LM101AFK/883	LM107JG/883
LF444CJ	LH0042H	LM101AH	LM107U
LF444CM	LH0042H-MIL	LM101AH/883	LM107W
LF444CN	LH0062CD	LM101AJ	LM107W/883
LF444MD/883	LH0062CH	LM101AJ/883	LM108AD
LF451CM	LH0062D	LM101AJ-14	LM108AH
LF453CM	LH0062H	LM101AJ-14/883	LM108AH/883
LH0003CH	LH0101ACK	LM101AJ8	LM108AJ
LH0003H	LH0101AK	LM101AJG	LM108AJ/883
LH0004CH	LH0101AK-MIL	LM101AJG/883	LM108AJ-8
LH0004H	LH0101CK	LM101AP	LM108AJ-8/883
LH0004H-MIL	LH0101K	LM101AU	LM108AJG
LH0021CK	LH0101K-MIL	LM101AU/883	LM108AL
LH0021K	LH1041G	LM101AW	LM108AP
LH0022CD	LH4161		LM108D

Multisim 14.0 Base Components

LM108D/883	LM111E	LM11CLN	LM139AJ
LM108H	LM111E/883	LM11H	LM139AW
LM108H/883	LM111H	LM124AD	LM139E
LM108J	LM111J-14	LM124AE	LM139J
LM108J/883	LM111J-8	LM124AE/883	LM139W
LM108J8	LM111W	LM124AFK	LM144H
LM108J-8	LM112H	LM124AJ	LM144H/883
LM108J8/883	LM112H/883	LM124AJ/883	LM146J
LM108J-8/883	LM117HVH	LM124AN	LM146J/883
LM108JG	LM117HVKSTL/883	LM124AW/883	LM149J
LM108JG/883	LM118D	LM124AWG/883	LM149J/883
LM108L	LM118FK	LM124D	LM158AD
LM108P	LM118H	LM124E	LM158AFK
LM10BH	LM118H/883	LM124E/883	LM158AH
LM10BLH	LM118J	LM124FK	LM158AH/883
LM10CH	LM118J/883	LM124J	LM158AJ
LM10CLH	LM118J8	LM124J/883	LM158AJG
LM10CLN	LM118J-8	LM124N	LM158AN
LM10CLN8	LM118J8/883	LM124W	LM158AP
LM10CLWM	LM118J-8/883	LM124W/883	LM158AWG/883
LM10CN	LM118JG	LM12CLK	LM158D
LM10CN8	LM118L	LM12LK	LM158FK
LM10CWM	LM118P	LM13700AN	LM158H
LM10H	LM11CH	LM13700M	LM158J
LM10H/883	LM11CLH	LM13700N	LM158JG

Multisim 14.0 Base Components

LM158N	LM211J-8	LM224NG	LM2901DG
LM158P	LM211M	LM224P	LM2901DR2G
LM160H	LM212H	LM239AJ	LM2901DTBR2G
LM160J	LM216AD	LM239DG	LM2901NG
LM160J-14	LM216AF	LM239DR2G	LM2901VDG
LM1877M-9	LM216AH	LM239DTBR2G	LM2901VDR2G
LM1877N-9	LM216D	LM239J	LM2901VDTBR2G
LM202H	LM216F	LM239NG	LM2901VNG
LM207D	LM216H	LM246J	LM2902DG
LM207H	LM218D	LM258AD	LM2902DR2G
LM207J	LM218H	LM258AH	LM2902DTBG
LM207P	LM218JG	LM258AJG	LM2902DTBR2G
LM208AD	LM218P	LM258AN	LM2902M
LM208AH	LM221H	LM258AP	LM2902MT
LM208AJ	LM224AD	LM258D	LM2902N
LM208AJ-8	LM224AJ	LM258DG	LM2902NG
LM208AN	LM224AN	LM258DMR2G	LM2902VD
LM208AP	LM224AP	LM258DR2G	LM2902VDG
LM208D	LM224D	LM258H	LM2902VDR2G
LM208H	LM224DG	LM258JG	LM2902VDTBG
LM208J	LM224DR2G	LM258N	LM2902VDTBR2G
LM208J-8	LM224DTBG	LM258NG	LM2902VN
LM208N	LM224DTBR2G	LM258P	LM2903DG
LM208P	LM224J	LM2878P	LM2903DMR2G
LM211H	LM224N	LM2900N	LM2903DR2

Multisim 14.0 Base Components

LM2903DR2G	LM293D	LM311M	LM324APWLE
LM2903NG	LM293DG	LM311N	LM324D
LM2904ADMR2G	LM293DMR2G	LM311N-14	LM324DBLE
LM2904AN	LM293DR2G	LM312H	LM324DG
LM2904ANG	LM301AD	LM318D	LM324DR2G
LM2904D	LM301AJ8	LM318H	LM324DTBG
LM2904DG	LM301AP	LM318J8	LM324DTBR2G
LM2904DMR2G	LM3046M	LM318J-8	LM324J
LM2904DR2G	LM307D	LM318M	LM324M
LM2904ITP	LM307N	LM318N	LM324MT
LM2904M	LM307P	LM318N8	LM324N
LM2904N	LM308AD	LM318P	LM324NG
LM2904NG	LM308AH	LM318S8	LM324P
LM2904P	LM308AJ	LM321AH	LM324PWLE
LM2904PW	LM308AJ-8	LM321H	LM324x2DBLE
LM2904QD	LM308AN	LM324AD	LM3301N
LM2904QP	LM308AN8	LM324ADG	LM3302N
LM2904VD	LM308D	LM324ADR2G	LM339AJ
LM2904VDG	LM308H	LM324ADTBG	LM339AM
LM2904VDMR2G	LM308J	LM324ADTBR2G	LM339AN
LM2904VDR2G	LM308J-8	LM324AJ	LM339DG
LM2904VN	LM308M	LM324AM	LM339DR2G
LM2904VNG	LM308N	LM324AN	LM339DTBR2G
LM2924M	LM308N8	LM324ANG	LM339J
LM2924N	LM311H	LM324AP	LM339M

Multisim 14.0 Base Components

LM339N	LM358M	LM556CM	LM6161J/883
LM339NG	LM358N	LM556CN	LM6161W/883
LM344H	LM358NG	LM607ACH	LM6161WG/883
LM346J	LM358P	LM607ACN	LM6162E/883
LM346M	LM358PW	LM607AMH	LM6162J/883
LM346N	LM358TP	LM607BCH	LM6162N
LM348D	LM359J	LM607BCN	LM6162W/883
LM348N	LM359M	LM607BMH	LM6162WG/883
LM348PW	LM359N	LM607CH	LM6164E/883
LM358AD	LM3900D	LM607CN	LM6164J
LM358ADR2G	LM3900M	LM6118E/883	LM6164J/883
LM358AH	LM3900N	LM6118J/883	LM6164W/883
LM358AJG	LM393DG	LM6118N	LM6164WG/883
LM358AM	LM393DMR2G	LM6132AIM	LM6165E/883
LM358AN	LM393DR2G	LM6132BIM	LM6165J
LM358AP	LM393NG	LM6132BIN	LM6165J/883
LM358BP	LM4250CH	LM6142AIM	LM6165W/883
LM358D	LM4250CM	LM6142AIN	LM6165WG/883
LM358DB	LM4250CN	LM6142AMJ-MLS	LM6171AIM
LM358DG	LM4250J-MIL	LM6142BIM	LM6171BIM
LM358DMR2G	LM4562HA	LM6142BIN	LM6171BIN
LM358DR2G	LM4562MA	LM6152ACM	LM6172AMJFQML
LM358H	LM4562NA	LM6152BCM	LM6172AMWGFQ ML
LM358J	LM555CM	LM6161E/883	LM6172IM
LM358JG	LM555CN	LM6161J	

Multisim 14.0 Base Components

LM6172IN	LM6361M	LM7121IM5	LM7332MM
LM6181IM	LM6361N	LM7131ACM	LM7341MF
LM6181IN	LM6362M	LM7131ACM5	LM7372IMA
LM6211MF	LM6362N	LM715CH	LM7372MR
LM6218AN	LM6364M	LM715CJ	LM741AH/883
LM6218AWM	LM6364N	LM715MH	LM741AJ-14/883
LM6218N	LM6365M	LM715MJ	LM741CH
LM6218WM	LM6365N	LM7171AIM	LM741CJ
LM6261J	LM637ACH	LM7171AIN	LM741CM
LM6261M	LM637AMH	LM7171AMJFQML	LM741CN
LM6261N	LM637BCH	LM7171BIM	LM741EH
LM6262M	LM637BMH	LM7171BIN	LM741EN
LM6262N	LM637CH	LM725AH	LM741H
LM6264J	LM637CN	LM725AH/883	LM741H/883
LM6264N	LM709AH	LM725CH	LM741J
LM6265J	LM709CH	LM725CN	LM741J/883
LM6265N	LM709CN	LM725H	LM741J-14/883
LM627ACH	LM709CN-8	LM725H/883	LM741W/883
LM627AMH	LM709H	LM7301IM	LM747AH
LM627BCH	LM710AMJ	LM7301IM5	LM747AJ
LM627BMH	LM710AMW	LM7321MA	LM748CH
LM627CH	LM710CH	LM7321MF	LM748CJ
LM627CN	LM710CN	LM7322MA	LM748CN
LM6313N	LM710H	LM7322MM	LM748H
LM6361J	LM7121IM	LM7332MA	LM759CH

Multisim 14.0 Base Components

LM759CP	LMC6001BIN	LMC6061AIN	LMC6084IM
LM759H/883	LMC6022IM	LMC6061AMJ/883	LMC6442AIM
LM759MH	LMC6024IM	LMC6061AMN	LMC6442IM
LM7805CT	LMC6032IM	LMC6061IM	LMC6442IN
LM7809CT	LMC6032IN	LMC6061IN	LMC6462AIM
LM7812CT	LMC6034IM	LMC6062AIM	LMC6462AIN
LM7815CT	LMC6035IBP	LMC6062AIN	LMC6462BIM
LM7818CT	LMC6035IM	LMC6062AMJ/883	LMC6462BIN
LM7824CT	LMC6035IMM	LMC6062AMN	LMC6464AIM
LM7905CT	LMC6035ITL	LMC6062IM	LMC6464AMWG- QML
LM7909CT	LMC6036IM	LMC6062IN	LMC6464BIM
LM7912CT	LMC6036IMT	LMC6064AIM	LMC6464BIN
LM7915CT	LMC6041AIM	LMC6064IM	LMC6482AIM
LM7918CT	LMC6041AIN	LMC6064IN	LMC6482AIN
LM7924CT	LMC6041IM	LMC6081AIM	LMC6482AMJ/883
LM8261M5	LMC6041IN	LMC6081AIN	LMC6482IM
LM8272MM	LMC6042AIM	LMC6081AMN	LMC6482IMM
LM833D	LMC6042AIN	LMC6081IM	LMC6482IN
LM833DG	LMC6042IM	LMC6081IN	LMC6482MN
LM833DR2G	LMC6042IN	LMC6082AIM	LMC6484AIM
LM833NG	LMC6044AIM	LMC6082AIN	LMC6484AIN
LMC555CH	LMC6044AIN	LMC6082AMN	LMC6484AMJ/883
LMC555CM	LMC6044IM	LMC6082IM	LMC6484AMWG/8 83
LMC555CN	LMC6044IN	LMC6082IN	
LMC6001AIN	LMC6061AIM	LMC6084AIM	LMC6484IM

Multisim 14.0 Base Components

LMC6484IN	LMC6772AIMM	LME49720NA	LMH6559MF
LMC6484MN	LMC6772BIM	LME49740MA	LMH6601MG
LMC6492AEM	LMC6772BIN	LME49740NA	LMH6609MA
LMC6492BEM	LMC7101AIM5	LME49990MA/NOP B	LMH6609MF
LMC6494AEM	LMC7101BIM5	LMH6321MR	LMH6611MK
LMC6494BEM	LMC7111BIM5	LMH6321TS	LMH6612MA
LMC6572AIM	LMC7211AIM	LMH6502MA	LMH6618MK
LMC6572BIM	LMC7211AIM5	LMH6502MT	LMH6619MA
LMC6574AIM	LMC7211BIM	LMH6503MA	LMH6622MA
LMC6574BIM	LMC7211BIM5	LMH6503MT	LMH6622MM
LMC660AIM	LMC7215IM	LMH6505MA	LMH6624J-QML
LMC660AIN	LMC7215IM5	LMH6505MM	LMH6624MA
LMC660AMD	LMC7221AIM	LMH6521SQ/NOPB	LMH6624MF
LMC660AMJ/883	LMC7221AIM5	LMH6550MA	LMH6628JFQML
LMC660CM	LMC7221BIM	LMH6550MM	LMH6628MA
LMC660CN	LMC7221BIM5	LMH6551MA	LMH6628WGFQML
LMC662AIM	LMC7225IM5	LMH6551MM	LMH6629MF
LMC662AIN	LMC8101BP	LMH6552MA	LMH6629SD
LMC662AMD	LMC8101MM	LMH6552SD	LMH6639MA
LMC662AMJ/883	LMC8101TP	LMH6553MR	LMH6639MF
LMC662CM	LME49710HA	LMH6553SD	LMH6642MA
LMC662CN	LME49710MA	LMH6554LE	LMH6642MF
LMC6762AIM	LME49710NA	LMH6555SQ	LMH6642MFXEP
LMC6762BIM	LME49720HA	LMH6559MA	LMH6643MA
LMC6772AIM	LME49720MA		LMH6643MAXEP

Multisim 14.0 Base Components

LMH6643MM	LMH6715MA	LMP2231BMA	LMP7717MA
LMH6644MA	LMH6718MA	LMP2231BMF	LMP7717MF
LMH6644MAXEP	LMH6720J-QML	LMP2232AMA	LMP7718MA
LMH6644MT	LMH6720MA	LMP2232AMM	LMP7718MM
LMH6645MA	LMH6720MF	LMP2232BMA	LMP7731MA
LMH6645MF	LMH6722J-QML	LMP2232BMM	LMP7731MF
LMH6646MA	LMH6722MA	LMP2234AMA	LMP7732MA
LMH6646MM	LMH6722MT	LMP2234AMT	LMP7732MM
LMH6647MA	LMH6723MA	LMP2234BMA	LMP8270MA
LMH6647MF	LMH6723MF	LMP2234BMT	LMP8271MA
LMH6655MA	LMH6733MQ	LMP7300MA	LMP8272MA
LMH6655MM	LMH6738MQ	LMP7300MM	LMP8275MA
LMH6657MF	LMH6739MQ	LMP7701MA	LMP8276MA
LMH6657MG	LMP2011MA	LMP7701MF	LMP8277MA
LMH6672MA	LMP2011MF	LMP7702MA	LMP8601MA
LMH6672MR	LMP2015MA	LMP7702MM	LMP8601QMA
LMH6702J-QML	LMP2015MF	LMP7704MA	LMP8602MA
LMH6702MA	LMP2016MA	LMP7704MT	LMP8602MM
LMH6702MF	LMP2016MM	LMP7707MF	LMP8602QMA
LMH6703MA	LMP2021MA	LMP7708MM	LMP8602QMM
LMH6703MF	LMP2021MF	LMP7709MT	LMP8603MA
LMH6714J-QML	LMP2022MA	LMP7711MK	LMP8603MM
LMH6714MA	LMP2022MM	LMP7712MM	LMP8603QMA
LMH6714MF	LMP2231AMA	LMP7715MF	LMP8603QMM
LMH6715JFQML	LMP2231AMF	LMP7716MM	LMP8645HVMMK

Multisim 14.0 Base Components

LMP8645MK	LMV602MM/NOPB	LMV761MF	LMV842MM
LMP8671MA/NOPB	LMV604MA/NOPB	LMV771MG	LMV844MA
LMP8672MA/NOPB	LMV604MT/NOPB	LMV772MA	LMV844MT
LMP8674MA/NOPB	LMV611MF/NOPB	LMV772MM	LMV851MG
LMV2011MA	LMV611MG/NOPB	LMV772QMM	LMV852MM
LMV2011MF	LMV612MA/NOPB	LMV774MT	LMV854MT
LMV321M5	LMV612MM/NOPB	LMV791MK	LMV861MG
LMV321M7	LMV614MA/NOPB	LMV792MM	LMV862MM
LMV324M	LMV614MT/NOPB	LMV793MA	LMV881LE/NOPB
LMV324MT	LMV641MA	LMV793MF	LMV931MF
LMV331M5	LMV641MG	LMV794MA	LMV931MG
LMV331M7	LMV651MG	LMV794MM	LMV932MA
LMV339M	LMV652MM	LMV796MF	LMV932MM
LMV339MT	LMV654MT	LMV797MM	LMV934MA
LMV342MA	LMV711M6	LMV821M5	LMV934MT
LMV342MM	LMV716MM	LMV821M7	LMV951MK
LMV358M	LMV7219M5	LMV822M	LMV981BL
LMV358MM	LMV7219M7	LMV822MM	LMV981MF
LMV393M	LMV721M5	LMV824M	LMV981MG
LMV393MM	LMV721M7	LMV824MT	LMV981TL
LMV551MG	LMV7271MF	LMV831MG	LMX321AUK+
LMV552MM	LMV7271MG	LMV832MM	LMX321AXK+
LMV554MT	LMV7291MG	LMV834MT	LMX324ASD+
LMV601MG/NOPB	LMV751M5	LMV841MG	LMX324AUD+
LMV602MA/NOPB	LMV761MA	LMV842MA	LMX358AKA+

Multisim 14.0 Base Components

LMX358ASA+	LPC660AIN	LPR201JC15	LT1001MJ8
LMX358AUA+	LPC660AMD	LPR201JC20	LT1002ACJ
LOSSLESS_LINE_TYP E1	LPC660AMJ/883	LPR201PC10	LT1002ACN
LOSSLESS_LINE_TYP E2	LPC660IM	LPR201PC12	LT1002AMJ
LOSSY_TRANSMISSI ON_LINE	LPC661AIM	LPR201PC15	LT1002CJ
	LPC661AIN	LPR201PC20	LT1002CN
	LPC661AMN	LPV321M5	LT1002MJ
LP124J	LPC661IM	LPV321M7	LT1006ACH
LP239D	LPC661IN	LPV324M	LT1006ACJ8
LP239J	LPC662AIM	LPV324MT	LT1006AMH
LP239N	LPC662AIN	LPV358MM	LT1006AMJ8
LP2901D	LPC662AMD	LPV358MX	LT1006CH
LP2901J	LPC662AMJ/883	LPV511MG	LT1006CJ8
LP2901N	LPC662IM	LPV521MG	LT1006CN8
LP2902M	LPC662IN	LT1001	LT1006MH
LP2902N	LPR200JC10	LT1001ACH	LT1006MJ8
LP311M	LPR200JC12	LT1001ACJ8	LT1006S8
LP311N	LPR200JC15	LT1001ACN8	LT1007ACH
LP324M	LPR200JC20	LT1001AMH/883	LT1007ACJ8
LP324N	LPR200PC10	LT1001AMJ8/883	LT1007ACN8
LP339D	LPR200PC12	LT1001CH	LT1007ACP
LP339J	LPR200PC15	LT1001CJ8	LT1007AMH
LP339M	LPR200PC20	LT1001CN8	LT1007AMJ8
LP339N	LPR201JC10	LT1001CS8	LT1007AMJG
LPC660AIM	LPR201JC12	LT1001MH	LT1007AML

Multisim 14.0 Base Components

LT1007AMP	LT1012ACN8	LT1013DMP	LT1021BCH-5
LT1007CDW	LT1012AMH	LT1013DN8	LT1021BCN8-10
LT1007CH	LT1012CH	LT1013DP	LT1021BCN8-5
LT1007CJ8	LT1012CN8	LT1013IP	LT1021BCN8-7
LT1007CN8	LT1012DH	LT1013MFK	LT1021BMH-10
LT1007CP	LT1012DN8	LT1013MH	LT1021DCS8-10
LT1007CS	LT1012MH	LT1013MJ8	LT1021DCS8-5
LT1007MH	LT1012S8	LT1013MJG	LT1021DCS8-7
LT1007MJ8	LT1013ACH	LT1013MP	LT1022ACH
LT1007MJG	LT1013ACJ8	LT1014ACJ	LT1022AMH
LT1007ML	LT1013ACP	LT1014AMJ	LT1022CH
LT1007MP	LT1013AIP	LT1014CJ	LT1022CN8
LT1008CH	LT1013AMFK	LT1014CN	LT1022MH
LT1008CN8	LT1013AMH	LT1014DN	LT1024ACN
LT1008MH	LT1013AMJ8	LT1014MJ	LT1024AMD
LT1008S8	LT1013AMP	LT1016CN8	LT1024CN
LT1010CDD	LT1013CH	LT1016CS8	LT1024MD
LT1010CH	LT1013CJ8	LT1016IN8	LT1028
LT1010CN8	LT1013CN8	LT1016IS8	LT1028ACH
LT1010CT	LT1013CP	LT1017CN8	LT1028ACJ8
LT1010MH	LT1013DD	LT1017CS8	LT1028ACN8
LT1011CN8	LT1013DID	LT1017CSW	LT1028AMH
LT1011CS8	LT1013DIP	LT1018CN8	LT1028AMJ8
LT1012	LT1013DMD	LT1018CS8	LT1028CH
LT1012ACH	LT1013DMJG	LT1018CSW	LT1028CJ8

Multisim 14.0 Base Components

LT1028CN8	LT1055AMH	LT1058AMJ	LT1078MJ8
LT1028CS	LT1055CH	LT1058CJ	LT1078S8
LT1028MH	LT1055CN8	LT1058CMJ	LT1079ACN
LT1028MJ8	LT1055MH	LT1058CN	LT1079AM
LT1037ACH	LT1055S8	LT1077ACH	LT1079CN
LT1037ACJ8	LT1056ACH	LT1077ACJ8	LT1079IN
LT1037ACN8	LT1056AMH	LT1077ACN8	LT1079ISW
LT1037ACP	LT1056CH	LT1077AIN8	LT1079MJ
LT1037AMH	LT1056CN8	LT1077AMH	LT1079SW
LT1037AMJ8	LT1056MH	LT1077AMJ8	LT1083CP
LT1037AMJG	LT1056S8	LT1077CH	LT1084CP
LT1037AML	LT1057ACH	LT1077CJ8	LT1084CT
LT1037AMP	LT1057ACJ8	LT1077CN8	LT1085CM
LT1037CDW	LT1057ACN8	LT1077IN8	LT1085CT
LT1037CH	LT1057AMH	LT1077IS8	LT1097CN8
LT1037CJ8	LT1057AMJ8	LT1077MH	LT1097S8
LT1037CN8	LT1057CH	LT1077MJ8	LT1101ACH
LT1037CP	LT1057CJ8	LT1077S8	LT1101ACJ8
LT1037CS	LT1057CN8	LT1078ACH	LT1101ACN8
LT1037MH	LT1057IS	LT1078ACN8	LT1101AIN8
LT1037MJ8	LT1057MH	LT1078AMJ8	LT1101AMH
LT1037MJG	LT1057MJ8	LT1078CN8	LT1101AMJ8
LT1037ML	LT1057S	LT1078IN8	LT1101CH
LT1037MP	LT1058ACJ	LT1078IS8	LT1101CJ8
LT1055ACH	LT1058ACN	LT1078MH	LT1101CN8

Multisim 14.0 Base Components

LT1101IN8	LT1122CMJ8	LT1178ACH	LT1189CJ8
LT1101MH	LT1122CS8	LT1178ACJ8	LT1189CN8
LT1101MJ8	LT1122DCJ8	LT1178ACN8	LT1189CS8
LT1101S	LT1122DCN8	LT1178AMH	LT1189MJ8
LT1102ACN8	LT1122DMJ8	LT1178AMJ8	LT118AH
LT1102CN8	LT1122DS8	LT1178CH	LT118AJ8
LT1102IN8	LT1124CN8	LT1178CJ8	LT1190CJ8
LT1112S8	LT1124CS8	LT1178CN8	LT1190CN8
LT1113ACN8	LT1125CN	LT1178IN8	LT1190CS8
LT1113CS8	LT1125CSW	LT1178MH	LT1190MJ8
LT1114S	LT1126CN8	LT1178MJ8	LT1191CJ8
LT1115CN8	LT1126CS8	LT1178S	LT1191CN8
LT1115CS	LT1127CN	LT1179ACJ	LT1191CS8
LT1116CN8	LT1127CSW	LT1179ACN	LT1191MJ8
LT1116CS8	LT1128CN8	LT1179AMJ	LT1192CJ8
LT1121CN8	LT1128CS8	LT1179CJ	LT1192CN8
LT1121CS8	LT1129CQ	LT1179CN	LT1192CS8
LT1122ACJ8	LT1129CS8	LT1179IN	LT1192MJ8
LT1122ACN8	LT1129CT	LT1179MJ	LT1193CJ8
LT1122AMJ8	LT1167CN8	LT1179S	LT1193CN8
LT1122BCJ8	LT1167CS8	LT1179SW	LT1193CS8
LT1122BCN8	LT1168CN8	LT1187CJ8	LT1193MJ8
LT1122BMJ8	LT1168CS8	LT1187CN8	LT1194CJ8
LT1122CCJ8	LT1169CN8	LT1187CS8	LT1194CN8
LT1122CCN8	LT1169CS8	LT1187MJ8	LT1194CS8

Multisim 14.0 Base Components

LT1194MJ8	LT1211CS8	LT1220CS8	LT1229MJ8
LT1195CJ8	LT1211MJ8	LT1220MJ8	LT1230CJ
LT1195CN8	LT1212CN	LT1221CN8	LT1230CN
LT1195CS8	LT1212CS	LT1221CS8	LT1230CS
LT1195MJ8	LT1213ACN8	LT1221MJ8	LT1230MJ
LT1200	LT1213AMJ8	LT1222CN8	LT1251CN
LT1201CN8	LT1213CN8	LT1222IS8	LT1251CS
LT1201CS8	LT1213CS8	LT1223CJ8	LT1252CN8
LT1202CN	LT1213MJ8	LT1223CN8	LT1252CS8
LT1202CS	LT1214CN	LT1223CS8	LT1253CN8
LT1206CN8	LT1214CS	LT1223MJ8	LT1253CS8
LT1206CR	LT1215ACN8	LT1224CN8	LT1254CN
LT1206CS8	LT1215AMJ8	LT1224CS8	LT1254CS
LT1206CY	LT1215CN8	LT1225CN8	LT1256CN
LT1207CS	LT1215CS8	LT1225CS8	LT1256CS
LT1208CN8	LT1215MJ8	LT1226CN8	LT1259CN
LT1208CS8	LT1216CN	LT1226CS8	LT1259CS
LT1209CN	LT1216CS	LT1227CN8	LT1260CN
LT1209CS	LT1217CN8	LT1227CS8	LT1260CS
LT1210CR	LT1217CS8	LT1227MJ8	LT1328CMS8
LT1210CS	LT1218CN8	LT1228CN8	LT1328CS8
LT1210CT7	LT1218CS8	LT1228CS8	LT1351CMS8
LT1211ACN8	LT1219CN8	LT1229CJ8	LT1351CN8
LT1211AMJ8	LT1219CS8	LT1229CN8	LT1351CS8
LT1211CN8	LT1220CN8	LT1229CS8	LT1352CN8

Multisim 14.0 Base Components

LT1352CS8	LT1365CN	LT1457CN8	LT1469CS8
LT1353CS	LT1365CS	LT1457S8	LT1490CMS8
LT1354CN8	LT1366CN8	LT1461-25	LT1490CN8
LT1354CS8	LT1366CS8	LT1461-3	LT1490CS8
LT1355CN8	LT1367CS	LT1461-33	LT1491CN
LT1355CS8	LT1368CN8	LT1461-4	LT1491CS
LT1356CN	LT1368CS8	LT1461-5	LT1492CN8
LT1356CS	LT1369CS	LT1462CN8	LT1492CS8
LT1357CN8	LT1394CMS8	LT1462CS8	LT1493CS
LT1357CS8	LT1395CS5	LT1463CN	LT1494CMS8
LT1358CN8	LT1395CS6	LT1463CS	LT1494CN8
LT1358CS8	LT1395CS8	LT1464CN8	LT1494CS8
LT1359CN	LT1396CDD	LT1464CS8	LT1495CN8
LT1359CS	LT1396CMS8	LT1465CN	LT1495CS8
LT1359CS14	LT1396CS8	LT1465CS	LT1496CN
LT1360CN8	LT1397CGN	LT1466LCN8	LT1496CS
LT1360CS8	LT1397CS	LT1466LCS8	LT1497CS
LT1361CN8	LT1398CS	LT1467LCS	LT1497CS8
LT1361CS8	LT1399CGN	LT1468CDD	LT1498CN8
LT1362CN	LT1399CS	LT1468CN8	LT1498CS8
LT1362CS	LT1413ACN8	LT1468CS8	LT1499CS
LT1363CN8	LT1413CN8	LT1468IDD	LT1521CMS8
LT1363CS8	LT1413S8	LT1468IN8	LT1521CS8
LT1364CN8	LT1431CN8	LT1468IS8	LT1529CQ
LT1364CS8	LT1431CS8	LT1469CN8	LT1529CT

Multisim 14.0 Base Components

LT1568CGN	LT1671CS8	LT1719CS8	LT1761ES5-5
LT1568IGN	LT1672CMS8	LT1719IS8	LT1761ES5-BYP
LT1630CN8	LT1672CN8	LT1720CDD	LT1761ES5-SD
LT1630CS8	LT1672CS8	LT1720CMS8	LT1762EMS8
LT1631CS	LT1672IMS8	LT1720CS8	LT1762EMS8-2.5
LT1632CN8	LT1672IN8	LT1720IDD	LT1762EMS8-3
LT1632CS8	LT1672IS8	LT1720IMS8	LT1762EMS8-3.3
LT1633CS	LT1673CN8	LT1720IS8	LT1762EMS8-5
LT1635CN8	LT1673CS8	LT1721CGN	LT1763CDE
LT1635CS8	LT1673IN8	LT1721CS	LT1763CDE-1.5
LT1636CDD	LT1673IS8	LT1721IGN	LT1763CDE-1.8
LT1636CMS8	LT1674CN	LT1722CS5	LT1763CDE-2.5
LT1636CN8	LT1674CS	LT1722CS8	LT1763CDE-3
LT1636CS8	LT1674IN	LT1723CMS8	LT1763CDE-3.3
LT1637CDD	LT1674IS	LT1723CS8	LT1763CDE-5
LT1637CMS8	LT1677CN8	LT1724CS	LT1763CS8
LT1637CN8	LT1677CS8	LT1739CFE	LT1763CS8-1.5
LT1637CS8	LT1678CS8	LT1739CUE	LT1763CS8-1.8
LT1638CDD	LT1679CS	LT1739IFE	LT1763CS8-2.5
LT1638CMS8	LT1711CMS8	LT1739IUE	LT1763CS8-3
LT1638CN8	LT1712CGN	LT1761ES5-1.8	LT1763CS8-3.3
LT1638CS8	LT1713CMS8	LT1761ES5-2	LT1763CS8-5
LT1639CN	LT1714CGN	LT1761ES5-2.5	LT1763IS8
LT1639CS	LT1715CMS	LT1761ES5-3	LT1763IS8-1.5
LT1671CMS8	LT1716CS5	LT1761ES5-3.3	LT1763IS8-1.8

Multisim 14.0 Base Components

LT1764EFE	LT1792CS8	LT1813CDD	LT1818IS5
LT1764EFE-1.5	LT1793CN8	LT1813CS8	LT1818IS8
LT1764EFE-1.8	LT1793CS8	LT1813DMS8	LT1819CMS8
LT1764EFE-2.5	LT1794CFE	LT1814CGN	LT1819CS8
LT1764EFE-3.3	LT1794CSW	LT1814CS	LT1819IMS8
LT1764EQ	LT1795CFE	LT1815CS5	LT1819IS8
LT1764EQ-1.5	LT1795CSW	LT1815CS6	LT1880CS5
LT1764EQ-1.8	LT1797CS5	LT1815CS8	LT1881CN8
LT1764EQ-2.5	LT1800CS5	LT1815IS5	LT1881CS8
LT1764EQ-3.3	LT1800CS8	LT1815IS6	LT1882CS
LT1782CS6	LT1801CDD	LT1815IS8	LT1884CN8
LT1783CS6	LT1801CMS8	LT1816ACMS	LT1884CS8
LT1784CS6	LT1801CS8	LT1816AIMS	LT1885CS
LT1784IS6	LT1802CS	LT1816CDD	LT1886CS8
LT1787CMS8	LT1806CS6	LT1816CMS8	LT1920CN8
LT1789CS8-1	LT1806CS8	LT1816CS8	LT1920CS8
LT1789CS8-10	LT1807CMS8	LT1816IDD	LT1962EMS8
LT1790ACS6-1.25	LT1807CS8	LT1816IMS8	LT1962EMS8-1.5
LT1790ACS6-2.048	LT1809CS6	LT1816IS8	LT1962EMS8-1.8
LT1790ACS6-2.5	LT1809CS8	LT1817CGN	LT1962EMS8-2.5
LT1790ACS6-3	LT1810CMS8	LT1817CS	LT1962EMS8-3
LT1790ACS6-3.3	LT1810CS8	LT1817IGN	LT1962EMS8-3.3
LT1790ACS6-4.096	LT1812CS5	LT1817IS	LT1962EMS8-5
LT1790ACS6-5	LT1812CS6	LT1818CS5	LT1963EFE
LT1792CN8	LT1812CS8	LT1818CS8	LT1963EFE-1.5

Multisim 14.0 Base Components

LT1963EFE-1.8	LT2179ACS	LT6004IDD	LT6202CS5
LT1963EFE-2.5	LT2179CS	LT6004IMS8	LT6202CS8
LT1963EFE-3.3	LT318A	LT6005CDHC	LT6203CDD
LT1970CFE	LT318AJ8	LT6005CGN	LT6203CMS8
LT1990CS8	LT318AN8	LT6005HDHC	LT6203CS8
LT1991CDD	LT6000CDCB	LT6005HGN	LT6204CGN
LT1991CMS	LT6000IDCB	LT6005IDHC	LT6204CS
LT1993CUD-10	LT6001CDD	LT6005IGN	LT6205CS5
LT1993CUD-2	LT6001CMS8	LT6010CDD	LT6206CMS8
LT1993CUD-4	LT6001IDD	LT6010CS8	LT6207CGN
LT1994CDD	LT6001IMS8	LT6011CDD	LT6220CS5
LT1994CMS8	LT6002CDHC	LT6011CMS8	LT6220CS8
LT1995CDD	LT6002CGN	LT6011CS8	LT6221CDD
LT1995CMS	LT6002IDHC	LT6012CGN	LT6221CS8
LT1995IDD	LT6002IGN	LT6012CS	LT6222CGN
LT1995IMS	LT6003CDC	LT6100CDD	LT6230CS6
LT1996CDD	LT6003CS5	LT6100CMS8	LT6231CDD
LT1996CMS	LT6003HDC	LT6200CS6	LT6231CS8
LT2078ACS8	LT6003HS5	LT6200CS6-10	LT6232CGN
LT2078AIS8	LT6003IDC	LT6200CS6-5	LT6233CS6
LT2078CS8	LT6003IS5	LT6200CS8	LT6234CDD
LT2079ACS	LT6004CDD	LT6200CS8-10	LT6234CS8
LT2079CS	LT6004CMS8	LT6200CS8-5	LT6235CGN
LT2178ACS8	LT6004HDD	LT6201CDD	LT6235IGN
LT2178CS8	LT6004HMS8	LT6201CS8	LT6402CUD-12

Multisim 14.0 Base Components

LT6402CUD-20	LT6600-5	LTC1050MH	LTC1151CSW
LT6402CUD-6	LT6650CS5	LTC1050MJ8	LTC1152CN8
LT6402IUD-12	LT6700CDCB-1	LTC1051ACJ8	LTC1152CS8
LT6402IUD-20	LT6700CDCB-2	LTC1051ACN8	LTC1250CN8
LT6402IUD-6	LT6700CDCB-3	LTC1051ACS	LTC1250CS8
LT6411CUD	LT6700CS6-1	LTC1051AMJ8	LTC1440CDD
LT6411IUD	LT6700CS6-2	LTC1051CJ8	LTC1440CMS8
LT6552CDD	LT6700CS6-3	LTC1051CN8	LTC1440CN8
LT6552CS8	LTC1043CN	LTC1051CS	LTC1440CS8
LT6552IDD	LTC1043CSW	LTC1051MJ8	LTC1441CN8
LT6552IS8	LTC1047CN8	LTC1052CD	LTC1441CS8
LT6553CGN	LTC1047CS	LTC1052CP	LTC1442CN8
LT6553IGN	LTC1049CJ8	LTC1052CS	LTC1442CS8
LT6557CDHC	LTC1049CN8	LTC1052MD	LTC1443CDHD
LT6557CGN	LTC1049CS8	LTC1052MP	LTC1443CN
LT6557IDHC	LTC1050ACH	LTC1053CN	LTC1443CS
LT6557IGN	LTC1050ACJ8	LTC1053CS	LTC1444CDHD
LT6558CDHC	LTC1050ACN	LTC1053CSW	LTC1444CN
LT6558CGN	LTC1050ACN8	LTC1100CN8	LTC1444CS
LT6558IDHC	LTC1050AMH	LTC1100CSW	LTC1444IDHD
LT6558IGN	LTC1050AMJ8	LTC1150CJ8	LTC1444IN
LT6559CUD	LTC1050CH	LTC1150CN8	LTC1444IS
LT6600-10	LTC1050CJ8	LTC1150CS8	LTC1445CDHD
LT6600-2.5	LTC1050CN	LTC1150MJ8	LTC1445CN
LT6600-20	LTC1050CN8	LTC1151CN8	LTC1445CS

Multisim 14.0 Base Components

LTC152	LTC2051CMS10	LTC6241HS8	LVT22V10-7A
LTC1540CDD	LTC2052CGN	LTC6241IDD	LVT22V10-7N
LTC1540CMS8	LTC2052CS	LTC6241IS8	LVT22V10B7A
LTC1540CS8	LTC2053CDD	LTC6242CDHC	M37702S1AFP
LTC1541CDD	LTC2053CMS8	LTC6242CGN	M37702S1BFP
LTC1541CMS8	LTC2053HDD	LTC6242HGN	M6060P-E3/45
LTC1541CS8	LTC2053HMS8	LTC6242IDHC	M68AF031AL_SO28
LTC1542CDD	LTC2053IMS8-SYNC	LTC6242IGN	M68AF127BL_SO32
LTC1542CMS8	LTC2054CS5	LTC6244CDD	M68AF511AL_SO32
LTC1542CS8	LTC2055CDD	LTC6244CMS8	M68AW031AL_SO28
LTC1563-2CGN	LTC2055CMS8	LTC6244HMS8	M68AW064FL_FBG A48
LTC1563-3CGN	LTC6078CDD	LTC6244IDD	M68AW128ML_SO44
LTC1798CS8	LTC6078CMS8	LTC6244IMS8	M68AW256ML_SO44
LTC1798CS8-2.5	LTC6079CDHC	LTC6800HDD	M68AW511AL_SO32
LTC1798CS8-3	LTC6079CGN	LTC6800HMS8	M68AW512DL_FBG A48
LTC1798CS8-4.1	LTC6101ACMS8	LTC6910-1CTS8	M68AW512ML_SO44
LTC1798CS8-5	LTC6101BCS5	LTC6910-2CTS8	MAC08MT1G
LTC1841CS8	LTC6240CS5	LTC6910-3CTS8	MAC12HCDG
LTC1842CS8	LTC6240CS8	LTC6911CMS-1	MAC15-10
LTC1966CMS8	LTC6240HS5	LTC6911CMS-2	MAC15-4
LTC1967CMS8	LTC6240HS8	LTC7652CH	MAC15-6
LTC1968CMS8	LTC6240IS5	LTR-516AD	
LTC2050CS5	LTC6240IS8	LVL_BARGRAPH	
LTC2050CS6	LTC6241CDD	LVM_CURRENT	
LTC2050CS8	LTC6241CS8	LVM_VOLTAGE	

Multisim 14.0 Base Components

MAC15-8	MAC223A-4	MAT02EH	MAX1421_FP48
MAC15A-10	MAC223A-6	MAT02FH	MAX1422_FP48
MAC15A-4	MAC223A-8	MAT03EH	MAX1444_FP32
MAC15A-6	MAC224-10	MAT03FH	MAX1446_FP32
MAC15A-8	MAC224-4	MAT04AY	MAX1449_FP32
MAC210-10	MAC224-6	MAT04EY	MAX15006AASA+
MAC210-4	MAC224-8	MAT04FP	MAX15006AATT+
MAC210-6	MAC224A-10	MAT04FS	MAX15007AASA+
MAC210-8	MAC224A-4	MAT04FY	MAX15007AATT+
MAC210A-10	MAC224A-6	MAX1180_FP48	MAX1966_SO8
MAC210A-4	MAC224A-8	MAX1181_FP48	MAX1967_SO10
MAC210A-6	MAC228-10	MAX1182_FP48	MAX209ENG
MAC210A-8	MAC228-4	MAX1183_FP48	MAX213EAI
MAC212-10	MAC228-6	MAX1184_FP48	MAX218CPP
MAC212-4	MAC228-8	MAX1185_FP48	MAX263_DIP28
MAC212-6	MAC228A-10	MAX1195_FP48	MAX264_DIP28
MAC212-8	MAC228A-4	MAX1197_FP48	MAX267_DIP24
MAC212A-10	MAC228A-6	MAX1198_FP48	MAX268_DIP24
MAC212A-4	MAC228A-8	MAX1284_SO8	MAX2740ECM
MAC212A-6	MAC23A-10	MAX1285_SO8	MAX274ACNG
MAC212A-8	MAG_CMP4	MAX1290_SO28	MAX274ACWI
MAC223-10	MAG_OL	MAX1291_SO28	MAX274BCNG
MAC223-4	MAG_OL_RELAY	MAX1292_SO24	MAX274BCWI
MAC223-6	MAGNETIC_CORE_	MAX1293_SO24	MAX280_SO16
MAC223-8	VIRTUAL	MAX1420_FP48	MAX281A_SO16

Multisim 14.0 Base Components

MAX291_SO16	MAX4038AAUA+	MAX4071AUA+	MAX4090ELT+T
MAX292_SO16	MAX4038EBL+T	MAX4072ATA+	MAX4090EUT+
MAX295_SO16	MAX4038ETA+	MAX4072AUA+	MAX4090EXT+
MAX296_SO16	MAX4038EUA+	MAX4073TAUT+	MAX409ACPA+
MAX4004EUT+	MAX4039EBL+T	MAX4073TAXK+	MAX409ACSA+
MAX4006EUT+	MAX4039ETB+T	MAX407CPA+	MAX409AEPA
MAX4007EUT+	MAX4039EUB+	MAX407CSA+	MAX409AESA+
MAX4008EUT+	MAX403CPA	MAX407EPA+	MAX409AMJA
MAX4012ESA+	MAX403CSA	MAX407ESA+	MAX409BCPA+
MAX4012EUK+	MAX403EPA	MAX407MJA	MAX409BCSA+
MAX4016ESA+	MAX403ESA	MAX4080FASA+	MAX409BEPA+
MAX4016EUA+	MAX4069AUB+	MAX4080FAUA+	MAX409BESA+
MAX4018EEE+	MAX406ACPA+	MAX4080SASA+	MAX4100ESA
MAX4018ESD+	MAX406ACSA+	MAX4080SAUA+	MAX4100ESA+
MAX4020EEE+	MAX406AEPA+	MAX4080TASA+	MAX4100EUA+
MAX4020ESD+	MAX406AESA+	MAX4080TAUA+	MAX4101ESA
MAX402CPA	MAX406AMJA	MAX4081FASA+	MAX4101ESA+
MAX402CSA	MAX406BCPA+	MAX4081FAUA+	MAX4104ESA
MAX402EPA	MAX406BCSA+	MAX4081SASA+	MAX4104ESA+
MAX402ESA	MAX406BEPA+	MAX4081SAUA+	MAX4104EUK+
MAX4032EUT+	MAX406BESA+	MAX4081TASA+	MAX4105ESA+
MAX4032EXT+	MAX406BMJA	MAX4081TAUA+	MAX4105EUK+T
MAX4036AAXK+	MAX4070ATA+	MAX4090AALT+T	MAX4106ESA
MAX4036EXK+	MAX4070AUA+	MAX4090AAUT+	MAX4106ESA+
MAX4037EUT+	MAX4071ATA+	MAX4090AAXT+	MAX4107ESA

Multisim 14.0 Base Components

MAX4107ESA+	MAX4122EUK+	MAX4131EBT+	MAX4163ESA+
MAX4108ESA	MAX4124EUK+	MAX4131ESA+	MAX4163EUA+
MAX4108ESA+	MAX4126ESA+	MAX4131EUA+	MAX4164ESD+
MAX4109ESA+	MAX4126EUA+	MAX4132ESA+	MAX4165EUK+
MAX410BCPA	MAX4128ESA+	MAX4132EUA+	MAX4166ELA+
MAX410BCSA	MAX4128EUA+	MAX4133ESD	MAX4166EPA+
MAX410BCSA+	MAX4129ESD+	MAX4134ESD+	MAX4166ESA+
MAX410BEPA	MAX412BCPA	MAX414BCPD	MAX4166EUA+
MAX410BESA	MAX412BCPA+	MAX414BCSD	MAX4167EPA+
MAX410CPA	MAX412BCSA	MAX414BCSD+	MAX4167ESA+
MAX410CPA+	MAX412BCSA+	MAX414BEPD	MAX4168EPD+
MAX410CSA	MAX412BEPA	MAX414BESD	MAX4168ESD+
MAX410CSA+	MAX412BEPA+	MAX414BESD+	MAX4168EUB+
MAX410EPA	MAX412BESA	MAX414CPD	MAX4169EPD
MAX410EPA+	MAX412BESA+	MAX414CPD+	MAX4169ESD+
MAX410ESA+	MAX412CPA	MAX414CSD	MAX4172EUA+
MAX410ETA-T	MAX412CPA+	MAX414CSD+	MAX4173TESA+
MAX4112ESA+	MAX412CSA	MAX414EPD	MAX4173TEUT+
MAX4112EUA	MAX412CSA+	MAX414EPD+	MAX4178EPA+
MAX4113ESA+	MAX412EPA	MAX414ESD	MAX4178ESA+
MAX4117ESA+	MAX412EPA+	MAX414ESD+	MAX4178EUA+
MAX4118ESA+	MAX412ESA	MAX414MJD	MAX4178EUK+T
MAX4119EEE	MAX412ESA+	MAX4162ESA+	MAX4178MJA
MAX4119ESD+	MAX412MJA	MAX4162EUK+	MAX417CPA+
MAX4120ESD+	MAX4130EUK+	MAX4163EBL+	MAX417CSA+

Multisim 14.0 Base Components

MAX417EPA+	MAX4190ESA+	MAX4205ESA	MAX4225ESA+
MAX417ESA+	MAX4190EUA	MAX4205EUA+	MAX4226ESD
MAX417MJA	MAX4194ESA+	MAX4206ETE	MAX4226EUB+
MAX4180ESA+	MAX4195ESA+	MAX4212EUK+	MAX4227ESA+
MAX4180EUT+T	MAX4196ESA+	MAX4213ESA+	MAX4228ESD+
MAX4181ESA+	MAX4197ESA+	MAX4213EUA+	MAX4228EUB+
MAX4181EUT+T	MAX4198ESA+	MAX4214EUK+	MAX4230AUK+
MAX4182ESA+	MAX4198EUA+	MAX4215ESA+	MAX4230AXK+
MAX4183ESD+	MAX4199ESA+	MAX4215EUA+	MAX4231ART+T
MAX4183EUB+	MAX4199EUA+	MAX4216ESA+	MAX4231AUT+
MAX4184ESA+	MAX419CPD+	MAX4216EUA+	MAX4231AXT+
MAX4185ESD	MAX419CSD+	MAX4217ESA+	MAX4231AYT+
MAX4185EUB+	MAX419EPD+	MAX4217EUA+	MAX4232AKA+
MAX4186ESD+	MAX419ESD+	MAX4218EEE+	MAX4232AUA+
MAX4187EEE+	MAX419MJD	MAX4218ESD+	MAX4233ABC+T
MAX4187ESD+	MAX4200ESA+	MAX4219EEE+	MAX4233AUB+
MAX4188EEE+	MAX4200EUK+	MAX4219ESD+	MAX4234ASD+
MAX4188ESD+	MAX4201ESA+	MAX4220EEE+	MAX4234AUD+
MAX4189EEE+	MAX4201EUK+T	MAX4220ESD+	MAX4236AESA+
MAX4189ESD+	MAX4202ESA+	MAX4222EEE+	MAX4236AEUA
MAX418CPD+	MAX4202EUK+T	MAX4222ESD+	MAX4236BESA+
MAX418CSD+	MAX4203ESA+	MAX4223ESA+	MAX4236BEUA+
MAX418EPD+	MAX4203EUA+	MAX4223EUT+	MAX4236EUT+
MAX418ESD+	MAX4204ESA+	MAX4224ESA+	MAX4237AESA+
MAX418MJD	MAX4204EUA+	MAX4224EUT+	MAX4237AEUA+

Multisim 14.0 Base Components

MAX4237BESA+	MAX4251EUA+	MAX4278EPA+	MAX4291EXK+
MAX4237BEUA+	MAX4252EBL+	MAX4278ESA+	MAX4292EBL+
MAX4237EUT+	MAX4252ESA+	MAX4278EUA+	MAX4292ESA+
MAX4238ASA+	MAX4252EUA+	MAX4278EUK+	MAX4292EUA+
MAX4238ATT+	MAX4253EBC+	MAX4278MJA	MAX4294ESD+
MAX4238AUT+	MAX4253ESD+	MAX427CPA+	MAX4294EUD+
MAX4239ASA+	MAX4253EUB+	MAX427CSA+	MAX4304ESA+
MAX4239ATT+	MAX4254ESD+	MAX427EPA+	MAX4304EUK+
MAX4239AUT+	MAX4255EUK+	MAX427ESA+	MAX4305ESA+
MAX4240EUK+	MAX4256ESA+	MAX427MJA	MAX4305EUK+
MAX4241ESA+	MAX4256EUA+	MAX4281ESA+	MAX4323EBT+T
MAX4241EUA+	MAX4257ESA+	MAX4281EUK+	MAX4323ESA+
MAX4242ESA+	MAX4257EUA+	MAX4282ESA+	MAX4323EUA
MAX4242EUA+	MAX4265ESA+	MAX4282EUA+	MAX4323EUT+
MAX4243ESD	MAX4265EUA+	MAX4284EEE	MAX4327ESD
MAX4243EUB+	MAX4266ESA+	MAX4284ESD	MAX4327EUB+
MAX4244ESD+	MAX4266EUA+	MAX4285ESA+	MAX4330EUK+
MAX4245AUT+	MAX4267ESA+	MAX4285EUT+	MAX4331ESA+
MAX4245AXT+	MAX4267EUA	MAX4286ESA+	MAX4331EUA+
MAX4247AUB+	MAX4268EEE+	MAX4286EUT-T	MAX4332ESA+
MAX4249ESD+	MAX4268ESD+	MAX4288ESD	MAX4333ESD+
MAX4249EUB+	MAX4269EEE	MAX4288EUB	MAX4333EUB+
MAX4250AAUK+	MAX4269ESD	MAX4289ESA+	MAX4334ESD+
MAX4250EUK+	MAX4270EEE	MAX4289EUT+	MAX4335EXT+
MAX4251ESA+	MAX4270ESD	MAX4291EUK+	MAX4336EUT-T

Multisim 14.0 Base Components

MAX4336EXT+	MAX4372TEBT+T	MAX437MJA	MAX4394EUD+
MAX4337EKA+	MAX4372TESA+	MAX4380EUT+	MAX4395ESD+
MAX4337EUA+	MAX4372TEUK+	MAX4380EXT+	MAX4395EUD+
MAX4338EUB+	MAX4373FESA+	MAX4381EUB+	MAX4396EUP+
MAX435CPD	MAX4373FEUA+	MAX4382EEE+	MAX4400AUK+
MAX435CSD	MAX4373HESA+	MAX4382ESD+	MAX4400AXK+
MAX435CSD+	MAX4373HEUA+	MAX4382EUD+	MAX4401AXT+
MAX435EPD	MAX4373TESA+	MAX4383EEE+	MAX4402AKA+
MAX435ESD	MAX4373TEUA+	MAX4383ESD+	MAX4402ASA+
MAX435ESD+	MAX4374FESD+	MAX4383ESE+	MAX4402AUA+
MAX435MJD	MAX4374FEUB+	MAX4383EUD+	MAX4403ASD+
MAX4361_SO8	MAX4374HESD+	MAX4384EUP+	MAX4403AUD+
MAX436CPD	MAX4374HEUB+	MAX4385EEUK+	MAX4412EUK+
MAX436CSD	MAX4374TESD+	MAX4386EESD+	MAX4412EXK+
MAX436CSD+	MAX4374TEUB+	MAX4386EEUD+	MAX4413EKA+
MAX436EPD	MAX4375FESD+	MAX4388ESD+	MAX4414ESA+
MAX436ESD	MAX4375FEUB+	MAX4388EUB	MAX4414EUA+
MAX436ESD+	MAX4375HESD+	MAX4389EUT+	MAX4415ESA+
MAX436MJD	MAX4375HEUB+	MAX4389EXT+	MAX4415EUA+
MAX4372FEBT+T	MAX4375TESD+	MAX4390EUK+	MAX4416ESA+
MAX4372FESA+	MAX4375TEUB+	MAX4390EXT+	MAX4416EUA+
MAX4372FEUK+	MAX437CPA	MAX4392ESA+	MAX4417ESA+
MAX4372HEBT+T	MAX437CSA+	MAX4392EUA+	MAX4417EUA+
MAX4372HESA+	MAX437EPA	MAX4393EUB+	MAX4418EUD+
MAX4372HEUK+	MAX437ESA+	MAX4394ESD+	MAX4419EUD+

Multisim 14.0 Base Components

MAX44241AUA+	MAX4432ESA	MAX4461HEUT+	MAX4476AUT+
MAX44241AUK+T	MAX4432EUA+	MAX4461TESA+	MAX4477ASA+
MAX44243ASD+	MAX4434ESA	MAX4461TETT+	MAX4477AUA+
MAX44243AUD+	MAX4434EUK+	MAX4461TEUT	MAX4478ASD+
MAX44251AKA+	MAX4435ESA	MAX4461UESA+	MAX4478AUD+
MAX44251AUA+	MAX4435EUK	MAX4461UETT+T	MAX4480AUK+
MAX44252ASD+	MAX4436ESA	MAX4461UEUT-T	MAX4480AXK+
MAX44264EWT+	MAX4436EUA+	MAX4462HESA+	MAX4481AUT+
MAX44265EWT+	MAX4437ESA	MAX4462HETT+	MAX4481AXT+
MAX44269EWL+	MAX4437EUA+	MAX4462HEUT+	MAX4482AKA+
MAX44280AXT+	MAX4450EUK+	MAX4462TESA	MAX4482ASA+
MAX44280AYT+	MAX4450EXK+	MAX4462TETT+T	MAX4482AUA+
MAX44281OANS+	MAX4451EKA+	MAX4462TEUT	MAX4483ASD+
MAX44281UANS+	MAX4451ESA+	MAX4462UESA	MAX4483AUD+
MAX44281VANS+	MAX4452EUK+	MAX4462UETT+	MAX4484AUK+
MAX44285FAUA+	MAX4452EXK+	MAX4464EUK+	MAX4484AXK+
MAX44285FAWA+T	MAX4453EKA+	MAX4464EXK+	MAX4486AKA+
MAX44285HAUA+	MAX4453ESA+	MAX4474EKA+	MAX4486ASA+
MAX44285HAWA+T	MAX4454ESD+	MAX4474ESA+	MAX4486AUA+
MAX44285LAUA+	MAX4454EUD+	MAX4474EUA+	MAX4487ASD+
MAX44285LAWA+T	MAX4460ESA+	MAX4475ASA+	MAX4487AUD+
MAX44285TAUA+	MAX4460ETT+	MAX4475ATT+	MAX4488ASA+
MAX44285TAWA+T	MAX4460EUT+T	MAX4475AUA+	MAX4488ATT+
MAX4430ESA+	MAX4461HESA+	MAX4475AUT+	MAX4488AUA+
MAX4430EUK+	MAX4461HETT+T	MAX4476ATT+T	MAX4488AUT+

Multisim 14.0 Base Components

MAX4489ASA+	MAX474CPA+	MAX479CSD+	MAX495MJA
MAX4489AUA+	MAX474CSA	MAX479EPD+	MAX496CPE+
MAX4490AUK+T	MAX474CSA+	MAX479ESD+	MAX496CSE+
MAX4490AXK+	MAX474CUA	MAX492CPA	MAX497CPE+
MAX4491AKA+	MAX474CUA+	MAX492CPA+	MAX497CSE+
MAX4491AUA+	MAX474EPA+	MAX492CSA	MAX5631_QFN68
MAX4492ASD+	MAX474ESA+	MAX492CSA+	MAX5632_QFN68
MAX4492AUD+	MAX474MJA	MAX492EPA+	MAX5633_QFN68
MAX4493AUK	MAX475CPD	MAX492ESA+	MAX6324AUT23-T
MAX4493AXK+	MAX475CSD	MAX492MJA	MAX6324AUT26-T
MAX4494AKA+	MAX475EPD	MAX494CPD	MAX6324AUT29+T
MAX4494ASA+	MAX475ESD	MAX494CPD+	MAX6324AUT31+T
MAX4494AUA+	MAX475MJD	MAX494CSD	MAX6324AUT44-T
MAX4495ASD+	MAX477EPA+	MAX494CSD+	MAX6324AUT46+T
MAX4495AUD+	MAX477ESA+	MAX494EPD+	MAX6324BUT23+T
MAX473CPA	MAX477EUA+	MAX494ESD+	MAX6324BUT26-T
MAX473CPA+	MAX477EUK+T	MAX494MJD	MAX6324BUT29+T
MAX473CSA	MAX477MJA	MAX495CPA	MAX6324BUT31-T
MAX473CSA+	MAX478ACPA+	MAX495CPA+	MAX6324BUT44-T
MAX473CUA	MAX478CPA+	MAX495CSA	MAX6324BUT46+T
MAX473CUA+	MAX478CSA+	MAX495CSA+	MAX6324CUT23+T
MAX473EPA+	MAX478EPA+	MAX495CUA	MAX6324CUT26+T
MAX473ESA+	MAX478ESA+	MAX495CUA+	MAX6324CUT29-T
MAX473MJA	MAX479ACPD	MAX495EPA+	MAX6324CUT31-T
MAX474CPA	MAX479CPD+	MAX495ESA+	MAX6324CUT44-T

Multisim 14.0 Base Components

MAX6324CUT46+T	MAX6324HUT23+T	MAX7404_DIP8	MAX803TEXR+
MAX6324DUT23+T	MAX6324HUT26-T	MAX7405_DIP8	MAX803ZEXR+
MAX6324DUT26+T	MAX6324HUT29+T	MAX7407_DIP8	MAX809JEUR+
MAX6324DUT29-T	MAX6324HUT31+T	MAX7408_SO8	MAX809LEUR+
MAX6324DUT31-T	MAX6324HUT44+T	MAX7409_SO8	MAX809LEXR+
MAX6324DUT44-T	MAX6324HUT46+T	MAX7410_SO8	MAX809MEUR+
MAX6324DUT46-T	MAX6460UT+	MAX7411_SO8	MAX809MEXR+
MAX6324EUT23+T	MAX6780LTA+	MAX7412_SO8	MAX809REUR+
MAX6324EUT26+T	MAX706RCPA	MAX7413_SO8	MAX809REXR+
MAX6324EUT29+	MAX706RCSA+	MAX7414_SO8	MAX809SEUR+
MAX6324EUT31-T	MAX706RCUA+	MAX7415_SO8	MAX809SEXR+
MAX6324EUT44-T	MAX706REPA	MAX7418_SO8	MAX809TEUR+
MAX6324EUT46+T	MAX706RESA+	MAX7419_SO8	MAX809TEXR+
MAX6324FUT23+T	MAX706REUA+	MAX7420_SO8	MAX809ZEXR+
MAX6324FUT26+T	MAX706RMJA	MAX7421_SO8	MAX810LEUR+
MAX6324FUT29-T	MAX706TCPA+	MAX7422_SO8	MAX810LEXR+
MAX6324FUT31-T	MAX706TCSA+	MAX7423_SO8	MAX810MEUR+
MAX6324FUT44-T	MAX706TCUA+	MAX7424_SO8	MAX810MEXR+
MAX6324FUT46+T	MAX706TEPA	MAX7425_SO8	MAX810REUR+
MAX6324GUT23-T	MAX706TESA+	MAX7426_SO8	MAX810REXR+T
MAX6324GUT26+T	MAX706TEUA+	MAX7427_SO8	MAX810SEUR+
MAX6324GUT29+T	MAX706TMJA	MAX803LEXR+	MAX810SEXR+
MAX6324GUT31-T	MAX7400_DIP8	MAX803MEXR+	MAX810TEUR+
MAX6324GUT44-T	MAX7401_DIP8	MAX803REXR+	MAX810TEXR+
MAX6324GUT46+T	MAX7403_DIP8	MAX803SEXR+	MAX810ZEXR+T

Multisim 14.0 Base Components

MAX9000ESA+	MAX9038BABT+T	MAX908MJD	MAX913ESA
MAX9000EUA+	MAX9038BEBT+T	MAX9092AKA+T	MAX913ESA+
MAX9002ESA+	MAX9075EUK+	MAX9092AUA+	MAX913EUA+
MAX9002EUA+	MAX9075EXK+	MAX9094ASD+	MAX913MJA
MAX9003ESA+	MAX9077EKA+	MAX9094AUD+	MAX913MSA/PR
MAX9003EUA+	MAX9077ESA+	MAX9117ESA+	MAX9140AAUK+
MAX9005ESA+	MAX9077EUA+	MAX9117EXK+	MAX9140AAXK+
MAX9005EUA+	MAX9077MSA/PR2	MAX9119EXK+	MAX9140EUK+
MAX9010EXT+	MAX907CPA	MAX9120ESA	MAX9140EXK+
MAX9011EUT+	MAX907CPA+	MAX9120EXK+	MAX9141EKA+
MAX9012ESA+	MAX907CSA	MAX912CPE	MAX9141ESA+
MAX9012EUA+	MAX907CSA+	MAX912CPE+	MAX9142EKA+
MAX9013ESA+	MAX907EPA	MAX912CSE	MAX9142ESA+
MAX9013EUA+	MAX907EPA+	MAX912CSE+	MAX9144ESD+
MAX9015AEKA+	MAX907ESA	MAX912EPE	MAX9144EUD+
MAX9026EBT+	MAX907ESA+	MAX912EPE+	MAX9201ESE+
MAX9030AUT+	MAX907MJA	MAX912ESE	MAX9201EUE+
MAX9030AXT+	MAX908CPD	MAX912ESE+	MAX9202ESD+
MAX9031AUK+	MAX908CPD+	MAX912MJE	MAX9202EUD+
MAX9031AXK+	MAX908CSD	MAX913CPA	MAX9203EKA+
MAX9032AKA+	MAX908CSD+	MAX913CPA+	MAX9203ESA+
MAX9032ASA+	MAX908EPD	MAX913CSA	MAX921CPA
MAX9032AUA+	MAX908EPD+	MAX913CSA+	MAX921CPA+
MAX9034ASD+	MAX908ESD	MAX913EPA	MAX921CSA
MAX9034AUD+	MAX908ESD+	MAX913EPA+	MAX921CSA+

Multisim 14.0 Base Components

MAX921CUA	MAX923ESA	MAX933CUA+	MAX942CPA
MAX921CUA+	MAX923ESA+	MAX933EPA	MAX942CPA+
MAX921EPA	MAX923MJA	MAX933EPA+	MAX942CSA
MAX921EPA+	MAX924CPE	MAX933ESA	MAX942CSA+
MAX921ESA	MAX924CPE+	MAX933ESA+	MAX942CUA+
MAX921ESA+	MAX924CSE	MAX934CPE	MAX942EPA
MAX921MJA	MAX924CSE+	MAX934CPE+	MAX942EPA+
MAX922CPA	MAX924EPE	MAX934CSE	MAX942ESA
MAX922CPA+	MAX924EPE+	MAX934CSE+	MAX942ESA+
MAX922CSA	MAX924ESE	MAX934EPE	MAX942EUA+
MAX922CSA+	MAX924ESE+	MAX934EPE+	MAX942MJA
MAX922CUA+	MAX924MJE	MAX934ESE	MAX944CPD
MAX922EPA	MAX932CPA	MAX934ESE+	MAX944CPD+
MAX922EPA+	MAX932CPA+	MAX941CPA	MAX944CSD
MAX922ESA	MAX932CSA	MAX941CPA+	MAX944CSD+
MAX922ESA+	MAX932CSA+	MAX941CSA	MAX944EPD
MAX922MJA	MAX932CUA+	MAX941CSA+	MAX944EPD+
MAX923CPA	MAX932EPA	MAX941CUA	MAX944ESD
MAX923CPA+	MAX932EPA+	MAX941EPA	MAX944ESD+
MAX923CSA	MAX932ESA	MAX941EPA+	MAX944MJD
MAX923CSA+	MAX932ESA+	MAX941ESA	MAX951EPA+
MAX923CUA	MAX933CPA	MAX941ESA+	MAX951ESA+
MAX923CUA+	MAX933CPA+	MAX941EUA+	MAX951EUA+
MAX923EPA	MAX933CSA	MAX941MJA	MAX951MJA
MAX923EPA+	MAX933CSA+	MAX942AUA+	MAX952EPA

Multisim 14.0 Base Components

MAX952EPA+	MAX9618AXA+	MAX9691ESA+	MAX987EUK+
MAX952ESA	MAX9619AXT+	MAX9691EUA+	MAX987EXK+
MAX952ESA+	MAX961ESA	MAX9692EPE+	MAX988ESA+
MAX952EUA+	MAX961ESA+	MAX9692ESE+	MAX988EUK+
MAX952MJA	MAX961EUA+	MAX9692EUB+	MAX988EXK+
MAX953EPA	MAX9620AXK+	MAX9693EEE+	MAX989EKA+
MAX953EPA+	MAX962ESA	MAX9693EPE+	MAX989ESA+
MAX953ESA	MAX9636AXT+	MAX9693ESE+	MAX989EUA+
MAX953ESA+	MAX9637AXA+	MAX975ESA+	MAX990EKA+
MAX953EUA+	MAX9638AVB+	MAX975EUA+	MAX990ESA+
MAX953MJA	MAX963ESA	MAX976ESA+	MAX990EUA+
MAX954EPA	MAX963ESD+	MAX976EUA+	MAX9910EXK+
MAX954EPA+	MAX9643TATA+T	MAX976MUA/PR2	MAX9911EWT+
MAX954ESA	MAX9643UATA+T	MAX977EEE+	MAX9911EXT+
MAX954ESA+	MAX9647AUK+T	MAX977ESD+	MAX9912EKA+
MAX954EUA+	MAX9647AXK+T	MAX978EEE+	MAX9913EUB+
MAX954MJA	MAX964ESA	MAX978ESE+	MAX9915EXT+
MAX9550EUA+	MAX9650ATA+	MAX985EBT+T	MAX9916EKA+
MAX9550EZK+	MAX9650AUA+	MAX985ESA+	MAX9917EUB+
MAX9551EUA+	MAX9650AZK+	MAX985EUK+	MAX9918ASA+
MAX9552EUD+	MAX9651ATA+	MAX985EXK+	MAX9919FASA+
MAX9600EUP+	MAX9651AUA+	MAX986ESA+	MAX9919NASA+
MAX9601EUP+	MAX965ESA+	MAX986EUK+	MAX991EKA+
MAX9602EUG+	MAX965EUA+	MAX986EXK+	MAX991ESA+
MAX9617AXT+	MAX9691EPA+	MAX987ESA+	MAX991EUA+

Multisim 14.0 Base Components

MAX9920ASA+	MAX997EUA+	MBR1035	MBR1240MFST1G
MAX9928FABT+	MAX998ESA+	MBR1035G	MBR1240MFST3G
MAX9928FAUA+	MAX998EUT+	MBR1045	MBR130LSFT1G
MAX9929FABT+	MAX999AAUK+5	MBR1045G	MBR130T1
MAX9929FAUA+	MAX999EUK+	MBR1045MFST1G	MBR130T1G
MAX992EKA+	MAXIM-MAXQ-HDR	MBR1045MFST3G	MBR130T3G
MAX992ESA+	MB6S-E3/80	MBR1060	MBR140ESFT1G
MAX992EUA+	MBD770DWT1G	MBR1060G	MBR140ESFT3G
MAX9934FART+	MBR030	MBR1080G	MBR140SFT1G
MAX9934FAUA+	MBR040	MBR1090G	MBR140SFT3G
MAX9934TART+	MBR0520L	MBR10H100CTG	MBR150G
MAX9934TAUA+	MBR0520LT1	MBR10H100CTHE3/ 45	MBR150RLG
MAX993ESD+	MBR0520LT1G	MBR10H100-E3/45	MBR1520
MAX993EUD+	MBR0520LT3G	MBR10L60CTG	MBR1530
MAX9943ATT+T	MBR0530	MBR1100G	MBR1535CT
MAX9943AUA+	MBR0530T1	MBR1100RLG	MBR1535CTG
MAX9944ASA+	MBR0530T1G	MBR12035CT	MBR1540
MAX9944ATA+T	MBR0530T3G	MBR12045CT	MBR1545CT
MAX994ESD+	MBR0540T1	MBR120ESFT1G	MBR1545CT-E3/45
MAX994EUD+	MBR0540T1G	MBR120ESFT3G	MBR1545CTG
MAX995ESD+	MBR0540T3G	MBR120LSFT1G	MBR160G
MAX995EUD+	MBR10100	MBR120LSFT3G	MBR160RLG
MAX996ESD+	MBR10100G	MBR120VLSFT1G	MBR16100CTG
MAX996EUD+	MBR10100MFST1G	MBR120VLSFT3G	MBR1635
MAX997ESA+	MBR10100MFST3G		MBR1635G

Multisim 14.0 Base Components

MBR1645	MBR20H200CT-E3/45	MBR30H100CTG	MBR360G
MBR1645G		MBR30H100MFST1G	MBR360RLG
MBR16H45-E3/45	MBR20L45CTG		MBR4015CTLG
MBR1H100SFT3G	MBR20L60CTG	MBR30H100MFST3G	MBR4015LWT
MBR20035CT	MBR230LSFT1G		MBR4015LWTG
MBR20045CT	MBR2520	MBR30H150CTG	
MBR20100	MBR2530	MBR30H30CTG	MBR4020
MBR20100CTG	MBR2535CT	MBR30H60CTG	MBR40250G
MBR20100CTH	MBR2535CTG	MBR30L45CTG	MBR40250TG
MBR20200CTG	MBR2535CTL	MBR30L60CTG	MBR4030
MBR2030CTLG	MBR2535CTLG	MBR3100G	MBR4040
MBR2035CT	MBR2540	MBR3100RLG	MBR4045PT-E3/45
MBR2045CT	MBR2545CT	MBR320M	MBR4045PTG
MBR2045CTG	MBR2545CTG	MBR320P	MBR4045WTG
MBR2045EMFST1G	MBR2H100SFT3G	MBR330M	MBR4060PT-E3/45
MBR2045EMFST3G	MBR30035CT	MBR330P	MBR40H100WTG
MBR2045MFST1G	MBR30045CT	MBR340	MBR40L45CTG
MBR2045MFST3G	MBR3020CT	MBR340G	MBR40L60CTG
MBR2060CTG	MBR3035CT	MBR340M	MBR41H100CTG
MBR2080CTG	MBR3035PT	MBR340P	MBR440MFST1G
MBR2090CTG	MBR3045CT	MBR340RLG	MBR440MFST3G
MBR20H100CT/45	MBR3045PT	MBR350RLG	MBR460MFST1G
MBR20H100CTG	MBR3045PTG	MBR3520	MBR460MFST3G
MBR20H150CTG	MBR3045STG	MBR3535	MBR5100MFST1G
	MBR3045WTG	MBR3545	MBR5100MFST3G
		MBR3545H	MBR540MFST1G

Multisim 14.0 Base Components

MBR540MFST3G	MBR745	MBRA320T3G	MBRB2535CTLG
MBR560MFST1G	MBR745-E3/45	MBRA340T3G	MBRB2535CTLT4G
MBR560MFST3G	MBR745G	MBRAF1100T3G	MBRB2545CTG
MBR5825	MBR7520	MBRAF1540T3G	MBRB2545CTT4G
MBR5825H	MBR7530	MBRAF2H100T3G	MBRB3030CT
MBR5831	MBR7535	MBRAF3200T3G	MBRB3030CTG
MBR5831H	MBR7540	MBRAF440T3G	MBRB3030CTL
MBR5H100MFST1G	MBR7545	MBRB1045G	MBRB3030CTLG
MBR6035	MBR760-E3/45	MBRB1045T4G	MBRB3030CTT4G
MBR6035B	MBR7H45-E3/45	MBRB1545CTG	MBRB3045CT-1G
MBR6035PF	MBR8035	MBRB1545CTT4	MBRB30H30CT-1G
MBR6045	MBR8045	MBRB1545CTT4G	MBRB30H60CT-1G
MBR6045B	MBR8H100MFST1G	MBRB1645T4G	MBRB30H60CTT4G
MBR6045H	MBR8H100MFST3G	MBRB20100CTG	MBRB4030
MBR6045PF	MBRA120ET3G	MBRB20100CTT4	MBRB4030G
MBR6045PTG	MBRA130LT3	MBRB20100CTT4G	MBRB4030T4G
MBR6045WTG	MBRA130LT3G	MBRB20200CTG	MBRB41H100CT-1G
MBR60H100CTG	MBRA140T3	MBRB20200CTT4	MBRB41H100CTT4
MBR60L45CTG	MBRA140T3G	MBRB20200CTT4G	G
MBR60L45WTG	MBRA160T3	MBRB2060CTG	MBRB60H100CTT4
MBR6535	MBRA160T3G	MBRB2060CTT4G	G
MBR6545	MBRA1H100T3G	MBRB20H100CTT4	MBRB8H100T4G
MBR7030WTL	MBRA210ET3G	G	MBRD1035CTL
MBR735	MBRA210LT3G	MBRB2515LG	MBRD1035CTLG
MBR735G	MBRA2H100T3G	MBRB2515LT4G	MBRD1035CTLT4G
			MBRD1045T4G

Multisim 14.0 Base Components

MBRD320G	MBRD660CTT4G	MBRM110ET3G	MBRS140T3
MBRD320RLG	MBRD835L	MBRM110LT1G	MBRS140T3G
MBRD320T4G	MBRD835LG	MBRM110LT3G	MBRS1540T3G
MBRD330G	MBRD835LT4G	MBRM120ET1G	MBRS190T3
MBRD330RLG	MBRF10H150CTG	MBRM120ET3G	MBRS190T3G
MBRD330T4G	MBRF10L60CTG	MBRM120LT1	MBRS2040LT3
MBRD340G	MBRF20100CTG	MBRM120LT1G	MBRS2040LT3G
MBRD340RLG	MBRF20200CTG	MBRM120LT3	MBRS230LT3G
MBRD340T4G	MBRF2045CTG	MBRM120LT3G	MBRS240LT3
MBRD350G	MBRF2060CTG	MBRM130LT1G	MBRS240LT3G
MBRD350RLG	MBRF20H100CTG	MBRM130LT3	MBRS260T3G
MBRD350T4G	MBRF20H150CTG	MBRM130LT3G	MBRS2H100T3G
MBRD360G	MBRF20L45CTG	MBRM140T1	MBRS3100T3G
MBRD360RLG	MBRF20L60CTG	MBRM140T1G	MBRS3200T3
MBRD360T4	MBRF20L80CTG	MBRM140T3	MBRS3200T3G
MBRD360T4G	MBRF2545CTG	MBRM140T3G	MBRS3201T3G
MBRD5H100T4G	MBRF30H100CTG	MBRM1H100T3G	MBRS320T3
MBRD620CTT4G	MBRF30H150CTG	MBRM2H100T3G	MBRS320T3G
MBRD630CTT4G	MBRF30H60CTG	MBRS1100T3	MBRS330T3G
MBRD640CTT4	MBRF30L45CTG	MBRS1100T3G	MBRS340T3
MBRD640CTT4G	MBRF30L60CTG	MBRS120T3	MBRS340T3G
MBRD650CTG	MBRF40250TG	MBRS120T3G	MBRS360BT3G
MBRD650CTT4G	MBRL030	MBRS130LT3	MBRS360T3
MBRD660CTG	MBRL040	MBRS130LT3G	MBRS360T3G
MBRD660CTRLG	MBRM110ET1G	MBRS130T3G	MBRS410ET3G

Multisim 14.0 Base Components

MBRS410LT3	MC1456G	MC1558SU	MC1748CU
MBRS410LT3G	MC1456P1	MC1558U	MC1748G
MBRS4201T3G	MC1458CD	MC1709AG	MC1748U
MBRS540T3	MC1458CG	MC1709AU	MC1776CD
MBRS540T3G	MC1458CP1	MC1709CG	MC1776CG
MBT2222ADW1T1G	MC1458CU	MC1709CP1	MC1776CP1
MBT35200MT1	MC1458D	MC1709CU	MC1776CU
MBT35200MT1G	MC1458G	MC1709G	MC1776G
MBT3904DW1T1G	MC1458P	MC1741CD	MC1776U
MBT3946DW1T1G	MC1458P1	MC1741CG	MC3301P
MBT3946DW1T2G	MC1458SD	MC1741CP1	MC3302DG
MC1436CD	MC1458SG	MC1741CU	MC3302DR2G
MC1436CG	MC1458SP1	MC1741G	MC3302DTBR2G
MC1436CP1	MC1458SU	MC1741SCD	MC3302PG
MC1436CU	MC1458U	MC1741SCG	MC3303D
MC1436D	MC1536G	MC1741SCP1	MC3303L
MC1436G	MC1536U	MC1741U	MC3303P
MC1436P1	MC1537L	MC1747CD	MC33071ADG
MC1436U	MC1539G	MC1747CG	MC33071ADR2G
MC1437L	MC1556G	MC1747CL	MC33071AP
MC1437P	MC1556U	MC1747CP2	MC33071APG
MC1439G	MC1558FK	MC1747G	MC33071D
MC1439P1	MC1558G	MC1747L	MC33071DG
MC1456CG	MC1558JG	MC1748CG	MC33071DR2G
MC1456CP1	MC1558SG	MC1748CP1	MC33071P

Multisim 14.0 Base Components

MC33071PG	MC33077D	MC33172P	MC33274ADG
MC33071U	MC33077DG	MC33174D	MC33274ADTBR2G
MC33072ADG	MC33077DR2G	MC33174P	MC33274APG
MC33072ADR2G	MC33077P	MC33178D	MC33274D
MC33072AP	MC33077PG	MC33178DG	MC33274P
MC33072APG	MC33078D	MC33178DMR2G	MC33282D
MC33072D	MC33078DG	MC33178DR2G	MC33282P
MC33072DG	MC33078DR2G	MC33178P	MC33284D
MC33072DR2G	MC33078P	MC33178PG	MC33284P
MC33072P	MC33078PG	MC33179D	MC3358P1
MC33072PG	MC33079D	MC33179DG	MC34001D
MC33072U	MC33079DG	MC33179DR2G	MC34001G
MC33074ADG	MC33079DR2G	MC33179DTBR2G	MC34001P
MC33074ADR2G	MC33079P	MC33179P	MC34001U
MC33074ADTBG	MC33079PG	MC33179PG	MC3401D
MC33074ADTBR2G	MC33161DG	MC33181D	MC3401P
MC33074APG	MC33161DMR2G	MC33181P	MC3403D
MC33074D	MC33161DR2G	MC33182D	MC3403DG
MC33074DG	MC33161PG	MC33182P	MC3403DR2G
MC33074DR2G	MC33171D	MC33184D	MC3403L
MC33074DTBG	MC33171DG	MC33184P	MC3403N
MC33074DTBR2G	MC33171DR2G	MC33272ADG	MC3403P
MC33074L	MC33171P	MC33272APG	MC3403PG
MC33074P	MC33171PG	MC33272D	MC3405L
MC33074PG	MC33172D	MC33272P	MC3405P

Multisim 14.0 Base Components

MC34071D	MC35071U	MCH3377-TL-H	MCP6002-E/P
MC34071P	MC35080AU	MCH3383-TL-H	MCP6002-I/MS
MC34071U	MC35080U	MCH3474-TL-E	MCP6002-I/P
MC34080D	MC35171U	MCH3474-TL-H	MCP6002-I/SN
MC34080P	MC35181U	MCH3484-TL-H	MCP6002T-E/MS
MC34084DW	MC3558G	MCH6203-TL-E	MCP6002T-E/SN
MC34084P	MC3558U	MCH6320-TL-E	MCP6004-E/P
MC34161DG	MC4558ACP1	MCH6321-TL-E	MCP6004-I/P
MC34161DMR2G	MC4558CD	MCH6336-TL-E	MCP6004-I/SL
MC34161DR2G	MC4558CG	MCH6336-TL-H	MCP6004-I/ST
MC34161PG	MC4558CP1	MCH6337-TL-E	MCP6004T-E/SL
MC34181D	MC4558CU	MCH6337-TL-H	MCP6004T-E/ST
MC34181P	MC4558G	MCH6421-TL-E	MCP601-I/P
MC3458D	MC4558U	MCH6436-TL-E	MCP601-I/SN
MC3458G	MC4741CD	MCH6534-TL-E	MCP601-I/ST
MC3458P1	MC4741CL	MCH6604-TL-E	MCP601T-I/OT
MC3458U	MC4741CP	MCP6001RT-E/OT	MCP6021-E/MS
MC3476G	MC4741L	MCP6001RT-I/OT	MCP6021-I/P
MC3476P1	MC68HC11D3CFBL	MCP6001T-E/LT	MCP6021-I/SN
MC3476U	MC68HC11D3CFN1	MCP6001T-E/OT	MCP6021-I/ST
MC35001G	MC68HC11D3CP1	MCP6001T-I/LT	MCP6021T-E/OT
MC35001U	MC68HC11E0CFN2	MCP6001T-I/OT	MCP6022-I/P
MC3503L	MC68HC11E1CFN2	MCP6001UT-E/OT	MCP6022-I/SN
MC3505L	MCH3209-TL-E	MCP6001UT-I/OT	MCP6022-I/ST
MC35071AU	MCH3377-TL-E	MCP6002-E/MC	MCP6023-I/P

Multisim 14.0 Base Components

MCP6023-I/SN	MCP6042-I/MS	MCP6064T-E/SL	MCP6141T-E/OT
MCP6023-I/ST	MCP6042-I/P	MCP6064T-E/ST	MCP6142-I/MS
MCP6024-I/P	MCP6042-I/SN	MCP606-I/P	MCP6142-I/P
MCP6024-I/SL	MCP6043-I/MS	MCP606-I/SN	MCP6142-I/SN
MCP6024-I/ST	MCP6043-I/P	MCP606-I/ST	MCP6143-I/MS
MCP602T-I/P	MCP6043-I/SN	MCP606T-I/OT	MCP6143-I/P
MCP602T-I/SN	MCP6043T-I/CH	MCP6071T-E/MNY	MCP6143-I/SN
MCP602T-I/ST	MCP6044-I/P	MCP6071T-E/OT	MCP6143T-E/CH
MCP6031-E/MS	MCP6044-I/SL	MCP6071T-E/SN	MCP6144-I/P
MCP6031-E/SN	MCP6044-I/ST	MCP6072T-E/MNY	MCP6144-I/SL
MCP6031T-E/OT	MCP604T-I/P	MCP6072T-E/SN	MCP6144-I/ST
MCP6032-E/MS	MCP604T-I/SL	MCP6074T-E/SL	MCP616-I/MS
MCP6032-E/SN	MCP604T-I/ST	MCP6074T-E/ST	MCP616-I/P
MCP6033-E/MS	MCP6051T-E/MNY	MCP607-I/P	MCP616-I/SN
MCP6033-E/SN	MCP6051T-E/OT	MCP607-I/SN	MCP617-I/MS
MCP6034-E/SL	MCP6051T-E/SN	MCP607-I/ST	MCP617-I/P
MCP6034-E/ST	MCP6052T-E/MNY	MCP608-I/P	MCP617-I/SN
MCP603T-I/CH	MCP6052T-E/SN	MCP608-I/SN	MCP618-I/MS
MCP603T-I/P	MCP6054T-E/SL	MCP608-I/ST	MCP618-I/P
MCP603T-I/SN	MCP6054T-E/ST	MCP609-I/P	MCP618-I/SN
MCP603T-I/ST	MCP6061T-E/MNY	MCP609-I/SL	MCP619-I/P
MCP6041-I/MS	MCP6061T-E/OT	MCP609-I/ST	MCP619-I/SL
MCP6041-I/P	MCP6061T-E/SN	MCP6141-I/MS	MCP619-I/ST
MCP6041-I/SN	MCP6062T-E/MNY	MCP6141-I/P	MCP621ST-E/OT
MCP6041T-I/OT	MCP6062T-E/SN	MCP6141-I/SN	MCP621T-E/MNY

Multisim 14.0 Base Components

MCP621T-E/SN	MCP6241UT-E/LT	MCP6274-E/P	MCP6291-E/MS
MCP622T-E/MF	MCP6241UT-E/OT	MCP6274-E/SL	MCP6291-E/P
MCP622T-E/SN	MCP6242-E/MS	MCP6274-E/ST	MCP6291-E/SN
MCP6231-E/MC	MCP6242-E/P	MCP6275-E/MS	MCP6291RT-E/OT
MCP6231-E/MS	MCP6242-E/SN	MCP6275-E/P	MCP6291T-E/OT
MCP6231-E/P	MCP6244-E/P	MCP6275-E/SN	MCP6292-E/MS
MCP6231-E/SN	MCP6244-E/SL	MCP6281-E/MS	MCP6292-E/P
MCP6231RT-E/OT	MCP6244-E/ST	MCP6281-E/P	MCP6292-E/SN
MCP6231T-E/OT	MCP624T-E/SL	MCP6281-E/SN	MCP6293-E/MS
MCP6231UT-E/LT	MCP624T-E/ST	MCP6281RT-E/OT	MCP6293-E/P
MCP6231UT-E/OT	MCP625T-E/MF	MCP6281T-E/OT	MCP6293-E/SN
MCP6232-E/MS	MCP625T-E/UN	MCP6282-E/MS	MCP6293T-E/CH
MCP6232-E/P	MCP6271-E/MS	MCP6282-E/P	MCP6294-E/P
MCP6232-E/SN	MCP6271-E/P	MCP6282-E/SN	MCP6294-E/SL
MCP6232T-E/MNY	MCP6271-E/SN	MCP6283-E/MS	MCP6294-E/ST
MCP6234-E/P	MCP6271RT-E/OT	MCP6283-E/P	MCP6295-E/MS
MCP6234-E/SL	MCP6271T-E/OT	MCP6283-E/SN	MCP6295-E/P
MCP6234-E/ST	MCP6272-E/MS	MCP6283T-E/CH	MCP6295-E/SN
MCP623T-E/CHY	MCP6272-E/P	MCP6284-E/P	MCP629T-E/ML
MCP6241-E/MC	MCP6272-E/SN	MCP6284-E/SL	MCP631T-E/MNY
MCP6241-E/MS	MCP6273-E/MS	MCP6284-E/ST	MCP631T-E/OT
MCP6241-E/P	MCP6273-E/P	MCP6285-E/MS	MCP631T-E/SN
MCP6241-E/SN	MCP6273-E/SN	MCP6285-E/P	MCP632T-E/MF
MCP6241RT-E/OT	MCP6273T-E/CH	MCP6285-E/SN	MCP632T-E/SN
MCP6241T-E/OT	MCP6273T-E/SN	MCP6286T-E/OT	MCP633T-E/CHY

Multisim 14.0 Base Components

MCP633T-E/SN	MCP6444T-E/ST	MCP6492-E/MS	MCP6541UT-E/OT
MCP635T-E/MF	MCP6471T-E/LTY	MCP6492-E/SN	MCP6541UT-I/LT
MCP635T-E/UN	MCP6471T-E/OT	MCP6492T-E/MNY	MCP6542-E/P
MCP6401RT-E/OT	MCP6472-E/MS	MCP6492T-E/MS	MCP6542-I/MS
MCP6401T-E/LT	MCP6472-E/SN	MCP6492T-E/SN	MCP6542-I/P
MCP6401T-E/OT	MCP6472T-E/MNY	MCP6494-E/SL	MCP6542-I/SN
MCP6401T-H/OT	MCP6472T-E/MS	MCP6494-E/ST	MCP6542T-E/MS
MCP6401UT-E/OT	MCP6472T-E/SN	MCP6494T-E/SL	MCP6542T-E/SN
MCP6402T-E/MNY	MCP6474-E/SL	MCP6494T-E/ST	MCP6543-E/P
MCP6402T-E/SN	MCP6474-E/ST	MCP651ST-E/OT	MCP6543-I/P
MCP6402T-H/SN	MCP6474T-E/SL	MCP651T-E/MNY	MCP6543-I/SN
MCP6404T-E/SL	MCP6474T-E/ST	MCP651T-E/SN	MCP6543T-E/MS
MCP6404T-E/ST	MCP6481T-E/LTY	MCP652T-E/MF	MCP6543T-E/SN
MCP6404T-H/SL	MCP6481T-E/OT	MCP652T-E/SN	MCP6543T-I/MS
MCP6406T-H/OT	MCP6482-E/MS	MCP653T-E/CHY	MCP6544-E/P
MCP6407T-H/SN	MCP6482-E/SN	MCP6541-E/P	MCP6544T-E/SL
MCP6409T-H/SL	MCP6482T-E/MNY	MCP6541-I/MS	MCP6544T-E/ST
MCP6421T-E/LTY	MCP6482T-E/MS	MCP6541-I/P	MCP6544T-I/P
MCP6421T-E/OT	MCP6482T-E/SN	MCP6541-I/SN	MCP6544T-I/SL
MCP6441T-E/LT	MCP6484-E/SL	MCP6541RT-E/OT	MCP6544T-I/ST
MCP6441T-E/OT	MCP6484-E/ST	MCP6541T-E/MS	MCP6546-E/P
MCP6442T-E/MNY	MCP6484T-E/SL	MCP6541T-E/OT	MCP6546-I/MS
MCP6442T-E/MS	MCP6484T-E/ST	MCP6541T-E/SN	MCP6546-I/P
MCP6442T-E/SN	MCP6491T-E/LTY	MCP6541T-I/LT	MCP6546-I/SN
MCP6444T-E/SL	MCP6491T-E/OT	MCP6541T-I/OT	MCP6546RT-E/OT

Multisim 14.0 Base Components

MCP6546RT-I/OT	MCP6548T-I/SN	MCP6567T-E/MS	MCP665T-E/UN
MCP6546T-E/MS	MCP6549-E/P	MCP6567T-E/SN	MCP669T-E/ML
MCP6546T-E/OT	MCP6549-I/P	MCP6569T-E/SL	MCP6H01T-E/MNY
MCP6546T-E/SN	MCP6549-I/SL	MCP6569T-E/ST	MCP6H01T-E/SN
MCP6546T-I/LT	MCP6549-I/ST	MCP659T-E/ML	MCP6H02T-E/MNY
MCP6546T-I/MS	MCP6549T-E/SL	MCP65R41T-1202E/CHY	MCP6H02T-E/SN
MCP6546T-I/OT	MCP6549T-E/ST		MCP6H04T-E/SL
MCP6546T-I/SN	MCP6549T-I/SL	MCP65R41T-2402E/CHY	MCP6H04T-E/ST
MCP6546UT-E/OT	MCP6549T-I/ST	MCP65R46T-1202E/CHY	MCP6H71-E/SN
MCP6546UT-I/LT	MCP654T-E/SL		MCP6H71T-E/MNY
MCP6547-E/P	MCP654T-E/ST	MCP65R46T-2402E/CHY	MCP6H71T-E/SN
MCP6547-I/MS	MCP655T-E/MF	MCP660T-E/ML	MCP6H72-E/SN
MCP6547-I/P	MCP655T-E/UN	MCP660T-E/SL	MCP6H72T-E/MNY
MCP6547-I/SN	MCP6561RT-E/OT	MCP660T-E/ST	MCP6H72T-E/SN
MCP6547T-E/MS	MCP6561T-E/LT	MCP661T-E/OT	MCP6H74-E/SL
MCP6547T-E/SN	MCP6561T-E/OT	MCP661T-E/SN	MCP6H74-E/ST
MCP6547T-I/MS	MCP6561UT-E/OT		MCP6H74T-E/SL
MCP6547T-I/SN	MCP6562T-E/MS	MCP662T-E/MF	MCP6H74T-E/ST
MCP6548-E/P	MCP6562T-E/SN	MCP662T-E/MS	MCP6H81-E/SN
MCP6548-I/MS	MCP6564T-E/SL	MCP662T-E/SN	MCP6H81T-E/MNY
MCP6548-I/P	MCP6564T-E/ST	MCP663T-E/CHY	MCP6H81T-E/SN
MCP6548-I/SN	MCP6566RT-E/OT	MCP663T-E/SN	MCP6H82-E/SN
MCP6548T-E/MS	MCP6566T-E/LT	MCP664T-E/SL	MCP6H82T-E/MNY
MCP6548T-E/SN	MCP6566T-E/OT	MCP664T-E/ST	MCP6H82T-E/SN
MCP6548T-I/MS	MCP6566UT-E/OT	MCP665T-E/MF	MCP6H84-E/SL

Multisim 14.0 Base Components

MCP6H84-E/ST	MCP6L71RT-E/OT	MCP6V06-E/SN	MCR1906_2
MCP6H84T-E/SL	MCP6L71T-E/MS	MCP6V06T-E/MNY	MCR1906_3
MCP6H84T-E/ST	MCP6L71T-E/OT	MCP6V07-E/MD	MCR1906_4
MCP6H91T-E/MNY	MCP6L71T-E/SN	MCP6V07-E/SN	MCR1906_6
MCP6H91T-E/SN	MCP6L72T-E/MS	MCP6V08-E/SN	MCR1906_8
MCP6H92T-E/MNY	MCP6L72T-E/SN	MCP6V08T-E/MNY	MCR22_2
MCP6H92T-E/SN	MCP6L74T-E/SL	MCP6V11T-E/OT	MCR22_3
MCP6H94T-E/SL	MCP6L74T-E/ST	MCP6V11UT-E/LT	MCR22_4
MCP6H94T-E/ST	MCP6L91RT-E/OT	MCP6V11UT-E/OT	MCR22_6
MCP6L01RT-E/OT	MCP6L91T-E/MS	MCP6V26T-E/MNY	MCR22_8
MCP6L01T-E/LT	MCP6L91T-E/OT	MCP6V26T-E/MS	MCR220_5
MCP6L01T-E/OT	MCP6L91T-E/SN	MCP6V26T-E/SN	MCR220_7
MCP6L01UT-E/OT	MCP6L92T-E/MS	MCP6V27T-E/MD	MCR220_9
MCP6L02T-E/MS	MCP6L92T-E/SN	MCP6V27T-E/MS	MCR221_5
MCP6L02T-E/SN	MCP6L94T-E/SL	MCP6V27T-E/SN	MCR221_7
MCP6L04T-E/SL	MCP6L94T-E/ST	MCP6V28T-E/MNY	MCR221_9
MCP6L04T-E/ST	MCP6N11-001E/SN	MCP6V28T-E/MS	MCR3818_10
MCP6L1RT-E/OT	MCP6N11T-001E/MNY	MCP6V28T-E/SN	MCR3818_2
MCP6L1T-E/MS	MCP6V01T-E/MNY	MCP6V31T-E/OT	MCR3818_3
MCP6L1T-E/OT	MCP6V01T-E/SN	MCP6V31UT-E/LT	MCR3818_4
MCP6L1T-E/SN	MCP6V02-E/MD	MCP6V31UT-E/OT	MCR3818_6
MCP6L2T-E/MS	MCP6V02-E/SN	MCR08BT1G	MCR3818_8
MCP6L2T-E/SN	MCP6V03-E/MNY	MCR08MT1G	MCR3835_1
MCP6L4T-E/SL	MCP6V03-E/SN	MCR100-3G	MCR3835_10
MCP6L4T-E/ST		MCR100-3RLG	MCR3835_2

Multisim 14.0 Base Components

MCR3835_3	MDA2506	MDA980-2	MINI-DIN5S
MCR3835_4	MDA3500	MDA980-3	MINI-DIN6
MCR3835_5	MDA3501	MDA980-4	MINI-DIN6S
MCR3835_6	MDA3502	MDA980-5	MIPS-EJTAG-HDR
MCR3835_7	MDA3504	MDA980-6	MJ11012G
MCR3835_8	MDA3506	MDA990-1	MJ11015G
MCR3835_9	MDA3508	MDA990-2	MJ11016G
MCR3935_1	MDA3510	MDA990-3	MJ11028G
MCR3935_10	MDA3550	MDA990-4	MJ11032G
MCR3935_2	MDA3551	MDA990-5	MJ11033G
MCR3935_3	MDA920A1	MDA990-6	MJ14002G
MCR3935_4	MDA920A2	MGP11N60ED	MJ15001G
MCR3935_5	MDA920A3	MGSF1N02LT1G	MJ15003G
MCR3935_6	MDA920A4	MGSF1N03LT1G	MJ15004G
MCR3935_7	MDA920A5	MGSF2N02ELT1G	MJ15015G
MCR3935_8	MDA920A6	MGW21N60ED	MJ15016G
MCR3935_9	MDA920A7	MHD20N06C	MJ15022G
MCR703AT4G	MDA920A8	MHD20N06G	MJ15023G
MCR706AT4G	MDA920A9	MHD20N06P	MJ15024G
MCR716T4G	MDA970A1	MICRO_4BIT_ALU	MJ15025G
MCR8SNG	MDA970A2	MINI-DIN3	MJ21193G
MDA2500	MDA970A3	MINI-DIN3S	MJ21194G
MDA2501	MDA970A5	MINI-DIN4	MJ21195G
MDA2502	MDA970A6	MINI-DIN4S	MJ21196G
MDA2504	MDA980-1	MINI-DIN5	MJ2955G

Multisim 14.0 Base Components

MJ4502G	MJD148T4G	MJD32CT4G	MJD47T4G
MJ802G	MJD200G	MJD32RLG	MJD50G
MJB41CG	MJD200RLG	MJD32T4G	MJD50T4G
MJB41CT4G	MJD200T4G	MJD340G	MJD5731T4G
MJB42CT4G	MJD210G	MJD340RLG	MJD6039T4G
MJB44H11G	MJD210RLG	MJD340T4G	MJE13003G
MJB44H11T4	MJD210T4	MJD350G	MJE13005G
MJB44H11T4G	MJD210T4G	MJD350T4G	MJE13007G
MJB45H11G	MJD243G	MJD41CRLG	MJE13009G
MJB45H11T4	MJD243T4G	MJD41CT4G	MJE15028G
MJB45H11T4G	MJD253-1G	MJD42C1G	MJE15029G
MJD112-1G	MJD253T4G	MJD42CG	MJE15030G
MJD112G	MJD2955-1G	MJD42CRLG	MJE15031G
MJD112RLG	MJD2955G	MJD42CT4G	MJE15032G
MJD112T4G	MJD2955T4G	MJD44E3T4G	MJE15033G
MJD117-1G	MJD3055G	MJD44H11-1G	MJE15034G
MJD117G	MJD3055T4G	MJD44H11G	MJE15035G
MJD117RLG	MJD31C1G	MJD44H11RLG	MJE170G
MJD117T4G	MJD31CG	MJD44H11T4G	MJE171G
MJD122G	MJD31CRLG	MJD44H11T5G	MJE172G
MJD122T4G	MJD31CT4G	MJD45H11-1G	MJE18002G
MJD127G	MJD31T4G	MJD45H11G	MJE18004G
MJD127T4	MJD32CG	MJD45H11RLG	MJE18006G
MJD127T4G	MJD32CRLG	MJD45H11T4G	MJE18008G
MJD148T4	MJD32CT4	MJD47G	MJE180G

Multisim 14.0 Base Components

MJE181G	MJE702G	MJL21196G	MM3Z3V6T1G
MJE182G	MJE703G	MJL3281AG	MM3Z3V9T1G
MJE200G	MJE800G	MJL4281AG	MM3Z43VT1G
MJE210G	MJE802G	MJL4302AG	MM3Z4V3ST1G
MJE243G	MJE803G	MJW18020G	MM3Z4V7T1G
MJE253G	MJF122G	MJW21196G	MM3Z5V1T1G
MJE270G	MJF127G	MJW3281AG	MM3Z5V6ST1G
MJE271G	MJF15030G	MKP3V120G	MM3Z6V8ST1G
MJE2955TG	MJF15031G	MKP3V120RLG	MM3Z8V2ST1G
MJE3055TG	MJF18004G	MKP3V240G	MM5Z10VT1G
MJE340G	MJF18008G	MKP3V240RLG	MM5Z12VT1G
MJE3439G	MJF2955G	MM3Z10VT1G	MM5Z15VT1G
MJE344G	MJF3055G	MM3Z12VST1G	MM5Z16VT1G
MJE350G	MJF31CG	MM3Z12VT1G	MM5Z18VT1G
MJE371G	MJF32CG	MM3Z15VST1G	MM5Z20VT1G
MJE4343G	MJF44H11G	MM3Z15VT1G	MM5Z24VT1G
MJE4353G	MJF45H11G	MM3Z18VT1G	MM5Z27VT1G
MJE5730G	MJH11021G	MM3Z20VT1G	MM5Z2V4ST1G
MJE5731AG	MJH11022G	MM3Z2V4T1G	MM5Z2V4T1G
MJE5731G	MJH6284G	MM3Z2V7T1G	MM5Z2V7T1G
MJE5742G	MJH6287G	MM3Z30VT1G	MM5Z33VT1G
MJE5850G	MJL1302AG	MM3Z36VT1G	MM5Z36VT1G
MJE5851G	MJL21193G	MM3Z39VT1G	MM5Z3V0T1G
MJE5852G	MJL21194G	MM3Z3V0T1G	MM5Z3V3T1G
MJE700G	MJL21195G	MM3Z3V3ST1G	MM5Z3V6T1G

Multisim 14.0 Base Components

MM5Z47VT1G	MMBD301LT3G	MMBT2484LT3G	MMBT5551LT1
MM5Z4V3T1G	MMBD301M3T5G	MMBT2907ALT1	MMBT5551LT1G
MM5Z4V7ST1G	MMBD352LT1G	MMBT2907ALT1G	MMBT5551LT3G
MM5Z4V7ST5G	MMBD353LT1G	MMBT2907ALT3G	MMBT5551M3T5G
MM5Z4V7T1G	MMBD4148	MMBT2907AM3T5 G	MMBT589LT1
MM5Z5V1ST1G	MMBD7000LT1	MMBT3904	MMBT589LT1G
MM5Z5V1T1G	MMBD7000LT1G	MMBT3904LT1	MMBT6428LT1G
MM5Z5V6ST1G	MMBD7000LT3G	MMBT3904LT1G	MMBT6429LT1G
MM5Z5V6T1G	MMBD717LT1G	MMBT3904LT3G	MMBT6517LT1
MM5Z6V2ST1G	MMBD914LT1	MMBT3904TT1G	MMBT6517LT1G
MM5Z6V2T1G	MMBD914LT1G	MMBT3906	MMBT6517LT3G
MM5Z6V8ST1G	MMBD914LT3G	MMBT3906TT1G	MMBT6520LT1
MM5Z6V8T1G	MMBF0201NLT1G	MMBT4401LT1	MMBT6520LT1G
MM5Z7V5T1G	MMBF170LT1G	MMBT4401LT1G	MMBTA06LT1
MM5Z8V2ST1G	MMBF4393LT1G	MMBT4401LT3G	MMBTA06LT1G
MM5Z8V2T1G	MMBF4393LT3G	MMBT4401M3T5G	MMBTA06LT3G
MM5Z9V1ST1G	MMBFJ175LT1G	MMBT4403LT1	MMBTA06WT1G
MM5Z9V1T1G	MMBFJ177LT1G	MMBT4403LT1G	MMBTA14LT1G
MMBD101LT1G	MMBFJ309LT1G	MMBT4403LT3G	MMBTA42
MMBD2835LT1G	MMBT2222A	MMBT4403M3T5G	MMBTA42LT1
MMBD2836LT1G	MMBT2222ALT1	MMBT489LT1G	MMBTA42LT1G
MMBD2837LT1G	MMBT2222ALT1G	MMBT5401LT1	MMBTA42LT3G
MMBD2838LT1G	MMBT2222ALT3G	MMBT5401LT1G	MMBTA56LT1
MMBD301LT1	MMBT2369ALT1G	MMBT5401LT3G	MMBTA56LT1G
MMBD301LT1G	MMBT2484LT1G		MMBTA56LT3G

Multisim 14.0 Base Components

MMBTA63LT1G	MMBZ27VAL	MMBZ6V8AL	MMSZ3V3T1G
MMBTA92	MMBZ27VALT1G	MMBZ9V1AL	MMSZ4678T1G
MMBTA92LT1G	MMBZ27VALT3G	MMDL770T1G	MMSZ4679T1G
MMBTA92LT3G	MMBZ27VCL	MMDL914T1	MMSZ4681T1G
MMBTH10-4LT1G	MMBZ27VCLT1G	MMDL914T1G	MMSZ4683T1G
MMBTH10LT1G	MMBZ33VAL	MMDL914T3G	MMSZ4688T1G
MMBTH10LT3G	MMBZ33VALT1G	MMFT960T1G	MMSZ4689T1G
MMBV105GLT1G	MMBZ33VCL	MMG05N60D	MMSZ4689T3G
MMBV3401LT1G	MMBZ5221BLT1G	MMJT350T1G	MMSZ4690T1G
MMBV3401LT3	MMBZ5222BLT1G	MMQA15VT1G	MMSZ4690T3G
MMBV3401LT3G	MMBZ5231BLT1G	MMQA20VT1G	MMSZ4691T1G
MMBZ10VAL	MMBZ5231BLT3G	MMQA20VT3G	MMSZ4692T1G
MMBZ12VAL	MMBZ5232BLT1G	MMQA5V6T1G	MMSZ4696T1G
MMBZ12VDL	MMBZ5240BLT1G	MMQA5V6T3G	MMSZ4699T1G
MMBZ15VAL	MMBZ5242BLT1G	MMQA6V2T1G	MMSZ4705T1G
MMBZ15VALT1	MMBZ5242BLT3G	MMSD301T1	MMSZ4706T1G
MMBZ15VALT1G	MMBZ5248BLT1G	MMSD301T1G	MMSZ4707T1G
MMBZ15VDL	MMBZ5248BLT3G	MMSD4148T1	MMSZ4715T1G
MMBZ15VDLT1G	MMBZ5254BLT1G	MMSD4148T1G	MMSZ5221BT1G
MMBZ15VDLT3G	MMBZ5256BLT1G	MMSD4148T3G	MMSZ5222BT1G
MMBZ18VAL	MMBZ5270BLT1G	MMSF3P02HD	MMSZ5225BT1G
MMBZ18VCL	MMBZ5V6AL	MMSZ10T1G	MMSZ5226BT1G
MMBZ20VAL	MMBZ5V6ALT1G	MMSZ12T1G	MMSZ5228BT1G
MMBZ20VALT1G	MMBZ5V6ALT3G	MMSZ2V7T1G	MMSZ5231BT1G
MMBZ20VCL	MMBZ6V2AL	MMSZ2V7T3G	MMSZ5231BT3G

Multisim 14.0 Base Components

MMSZ5234BT1G	MMT08B350T3G	MMUN2231LT1G	MPC-BDM-HDR
MMSZ5235BT1G	MMT10B230T3G	MMUN2232LT1G	MPS2907AG
MMSZ5235BT3G	MMT10B260T3G	MMUN2233LT1G	MPS2907ARLG
MMSZ5236BT1G	MMT10B310T3G	MMUN2234LT1G	MPS2907ARLRAG
MMSZ5239BT1G	MMT10B350T3G	MMUN2238LT1G	MPS2924
MMSZ5240BT1G	MMUN2111LT1G	MMVL3401T1G	MPS2925
MMSZ5242BT1G	MMUN2111LT3G	MONOSTABLE_VIRTUAL	MPS2926
MMSZ5242BT3G	MMUN2112LT1G		MPS3392
MMSZ5243BT1G	MMUN2113LT1G	MOS_N	MPS3393
MMSZ5245BT1G	MMUN2113LT3G	MOS_N_4T	MPS3395
MMSZ5246BT1G	MMUN2114LT1G	MOS_N_4T_DEP	MPS3638A
MMSZ5254BT1G	MMUN2114LT3G	MOS_N_DEP	MPS3644
MMSZ5258BT1G	MMUN2115LT1G	MOS_P	MPS3646
MMSZ5258BT3G	MMUN2116LT1G	MOS_P_4T	MPS3702
MMSZ5259BT1G	MMUN2130LT1G	MOS_P_4T_DEP	MPS3703
MMSZ5260BT1G	MMUN2131LT1G	MOS_P_DEP	MPS3704
MMSZ5262BT1G	MMUN2132LT1G	MOTOR_1A	MPS3707
MMSZ5263BT1G	MMUN2134LT1G	MOTOR_1C	MPS3711
MMT05B230T3G	MMUN2211LT1G	MOTOR_2A	MPS3826
MMT05B260T3G	MMUN2211LT3G	MOTOR_2C	MPS3827
MMT05B310T3G	MMUN2212LT1G	MOTOR_3A	MPS3904
MMT05B350T3G	MMUN2213LT1G	MOTOR_3C	MPS5172
MMT08B064T3G	MMUN2214LT1G	MOTOR_4A	MPS5179
MMT08B260T3G	MMUN2215LT1G	MOTOR_4C	MPS6512
MMT08B310T3G	MMUN2216LT1G	MOTOR_VIRTUAL	MPS6513

Multisim 14.0 Base Components

MPS6514	MPSA06RLRMG	MPSW06RLRAG	MR2406
MPS6515	MPSA06RLRPG	MPSW10	MR2406F
MPS6516	MPSA10	MPSW42	MR2500
MPS6517	MPSA18	MPSW45G	MR2501
MPS6518	MPSA20	MPSW51	MR2502
MPS6520	MPSA42	MPSW51A	MR2504
MPS6521	MPSA42G	MPSW51AG	MR2506
MPS6522	MPSA43	MPSW51ARLRAG	MR2508
MPS6523	MPSA43G	MPSW51ARLRPG	MR2510
MPS6531	MPSA55	MPSW51G	MR327
MPS6533	MPSA56	MPSW55	MR328
MPS6534	MPSA56G	MPSW56	MR330
MPS6562	MPSA56RLRAG	MR1120	MR331
MPS6565	MPSA56RLRMG	MR1366	MR500
MPS6566	MPSA56RLRPG	MR1376	MR5005
MPS6571	MPSA56ZL1G	MR1386	MR501
MPS8098	MPSA70	MR1396	MR5010
MPS8099	MPSA92	MR2400	MR502
MPS8598	MPSA93	MR2400F	MR5020
MPSA05	MPSH10	MR2401	MR5030
MPSA06	MPSL01	MR2401F	MR504
MPSA06G	MPSL51	MR2402	MR5040
MPSA06RL1G	MPSW01	MR2402F	MR5059
MPSA06RLG	MPSW01A	MR2404	MR506
MPSA06RLRAG	MPSW06G	MR2404F	MR5060

Multisim 14.0 Base Components

MR5061	MR836	MRF9011LT1_A	MSS1P4HM3/89A
MR508	MR850	MRF9011LT1_B	MSS1P6HM3/89A
MR510	MR851	MRF9411LT1	MSS2P3HM3/89A
MR750	MR852	MRF947T1	MTB20N20E
MR751	MR854	MRF9511LT1	MTB50P03HDLT4G
MR752	MR856	MRS1504T3G	MTD10P06HDL
MR754	MR860	MSB92T1G	MTD15N06V
MR756	MR861	MSD1328-RT1G	MTD1N60E
MR810	MR862	MSD602-RT1G	MTD1N80E
MR811	MR864	MSE1PJHM3/89A	MTD2955E
MR812	MR866	MSP3V3HM3/89A	MTD2N50E
MR813	MR870	MSP430P325IFN	MTD3055V
MR814	MR871	MSP430P325IPG	MTD3055VL
MR816	MR872	MSP430P325IPM	MTD4N20E
MR817	MR874	MSQA6V1W5T2G	MTD4P06
MR818	MR876	MSR1560G	MTD5N06
MR820	MRA4003T3G	MSR860G	MTD6N15T4G
MR821	MRA4004T3G	MSRD620CTG	MTD6N20ET4G
MR822	MRA4005T1G	MSRD620CTRG	MTH13N50
MR824	MRA4005T3G	MSRD620CTT4	MTH30N20
MR826	MRA4006T3G	MSRD620CTT4G	MTH5N100
MR830	MRA4007T3G	MSRD620CTT4RG	MTH8N60
MR831	MRF5711LT1	MSRF1560G	MTM10N100E
MR832	MRF5812	MSRF860G	MTM15N40
MR834	MRF9011LT1	MSS1P3LHM3/89A	MTM24N50E

Multisim 14.0 Base Components

MTM26N40E	MTP6N60/MC	MUN2233T1G	MUN5211DW1T1G
MTM8N60	MTP7N20	MUN2234T1G	MUN5211T1
MTP10N05E/MC	MTP8N50E	MUN2236T1G	MUN5211T1G
MTP12P10	MTP8P10	MUN2237T1G	MUN5212DW1T1G
MTP15N05E	MULTIPLIER	MUN2238T1G	MUN5212T1G
MTP15N06E	MUN2111T1G	MUN2240T1G	MUN5213DW1T1G
MTP20P06	MUN2112T1G	MUN5111DW1T1G	MUN5213DW1T3G
MTP25N06	MUN2113T1G	MUN5111T1G	MUN5213T1G
MTP25N06L	MUN2114T1G	MUN5112DW1T1G	MUN5214DW1T1G
MTP25N10E	MUN2115T1G	MUN5112T1G	MUN5214T1G
MTP2N50	MUN2135T1G	MUN5113DW1T1G	MUN5215DW1T1G
MTP2P50	MUN2138T1G	MUN5113T1G	MUN5215T1G
MTP2P50EG	MUN2141T1G	MUN5113T3G	MUN5216DW1T1G
MTP3055E/MC	MUN2211T1	MUN5114DW1T1G	MUN5230DW1T1G
MTP3055V	MUN2211T1G	MUN5114T1G	MUN5230T1G
MTP3055VL	MUN2211T3G	MUN5115DW1T1G	MUN5232DW1T1G
MTP30N08M	MUN2212T1G	MUN5115T1G	MUN5232T1G
MTP35N06E	MUN2213T1	MUN5116DW1T1G	MUN5233DW1T1G
MTP3N100	MUN2213T1G	MUN5131T1G	MUN5233T1G
MTP40N06M	MUN2214T1G	MUN5132T1G	MUN5235DW1T1G
MTP4N50	MUN2214T3G	MUN5133DW1T1G	MUN5237DW1T1G
MTP4N85	MUN2215T1G	MUN5133T1G	MUN5238T1G
MTP50N05EL	MUN2216T1G	MUN5135DW1T1G	MUN5240T1G
MTP50N06E	MUN2230T1G	MUN5135T1G	MUN5241T1G
MTP6N60	MUN2232T1G	MUN5140T1G	MUN5311DW1T1G

Multisim 14.0 Base Components

MUN5312DW1T1G	MUR115G	MUR1610CT	MUR260RLG
MUN5312DW1T2G	MUR115RLG	MUR1610CTG	MUR3005PT
MUN5313DW1T1G	MUR120G	MUR1615CT	MUR3010PT
MUN5314DW1T1G	MUR120RLG	MUR1615CTG	MUR3015PT
MUN5315DW1T1G	MUR130G	MUR1620CT	MUR3020PT
MUN5316DW1T1G	MUR130RLG	MUR1620CTG	MUR3020PTG
MUN5330DW1T1G	MUR140G	MUR1620CTRG	MUR3020WTG
MUN5333DW1T1G	MUR140RLG	MUR1640CTG	MUR3040PTG
MUN5334DW1T1G	MUR1505	MUR1660CTG	MUR3060PTG
MUN5335DW1T1G	MUR1510	MUR180EG	MUR3060WTG
MUN5336DW1T1G	MUR1510G	MUR180ERLG	MUR405
MUR10005CT	MUR1515	MUR2020RG	MUR405G
MUR10010CT	MUR1515G	MUR2100EG	MUR410
MUR10015CT	MUR1520	MUR2100ERLG	MUR4100EG
MUR10020CT	MUR1520G	MUR210G	MUR4100ERLG
MUR10150E	MUR1530	MUR210RLG	MUR410G
MUR105	MUR1540	MUR220G	MUR410RLG
MUR105G	MUR1540G	MUR220RLG	MUR415
MUR105RLG	MUR1550	MUR240G	MUR415G
MUR110	MUR1560	MUR240RLG	MUR415RLG
MUR1100EG	MUR1560G	MUR2505	MUR420
MUR1100ERLG	MUR160	MUR2510	MUR420G
MUR110G	MUR1605CT	MUR2515	MUR420RLG
MUR110RLG	MUR160G	MUR2520	MUR440G
MUR115	MUR160RLG	MUR260G	MUR440RLG

Multisim 14.0 Base Components

MUR460G	MUR840	MURB1620CTG	MURHB840CTT4
MUR460RLG	MUR840G	MURB1620CTRG	MURHB840CTT4G
MUR480EG	MUR850	MURB1620CTRT4G	MURHB860CTT4G
MUR480ERLG	MUR860	MURB1620CTT4	MURHD560T4G
MUR5005	MUR860G	MURB1620CTT4G	MURHD560W1T4G
MUR5010	MUR880EG	MURB1660CTG	MURHF860CTG
MUR5015	MURA105T3G	MURB1660CTT4G	MURHS160T3G
MUR5020	MURA110T3	MURD320T4	MURS105T3G
MUR550APFRLG	MURA110T3G	MURD320T4G	MURS110T3
MUR550PFG	MURA115T3G	MURD330T4G	MURS110T3G
MUR605CT	MURA120T3	MURD340T4G	MURS115T3
MUR610CT	MURA120T3G	MURD530T4G	MURS115T3G
MUR615CT	MURA130T3G	MURD550PFT4G	MURS120T3
MUR620CT	MURA140T3	MURD620CT	MURS120T3G
MUR620CTG	MURA140T3G	MURD620CTG	MURS140T3
MUR805	MURA160T3	MURD620CTT4	MURS140T3G
MUR805G	MURA160T3G	MURD620CTT4G	MURS160-E3/52T
MUR810	MURA205T3G	MURF1560G	MURS160T3
MUR8100EG	MURA210T3G	MURF1620CTG	MURS160T3G
MUR810G	MURA215T3	MURF1660CTG	MURS205T3G
MUR815	MURA215T3G	MURF550PFG	MURS210T3G
MUR815G	MURA220T3	MURF860G	MURS220T3
MUR820	MURA220T3G	MURH840CTG	MURS220T3G
MUR820G	MURA230T3G	MURH860CTG	MURS230T3
MUR830	MURA240T3G	MURHB840CTG	MURS230T3G

Multisim 14.0 Base Components

MURS240T3G	myRIO_MXP	MZ5524B	MZPY4.7
MURS310T3	MZ4099	MZ5525B	MZPY43
MURS320T3	MZ4100	MZ5526B	MZPY47
MURS320T3G	MZ4101	MZ5527B	MZPY5.1
MURS340T3	MZ4102	MZ5528B	MZPY5.6
MURS340T3G	MZ4103	MZ5529B	MZPY51
MURS360BT3G	MZ4104	MZ5530B	MZPY56
MURS360-E3/57T	MZ4614	MZPY10	MZPY6.2
MURS360T3	MZ4615	MZPY100	MZPY6.8
MURS360T3G	MZ4616	MZPY11	MZPY62
MURS480ET3G	MZ4617	MZPY12	MZPY68
MUSHROOM_HEAD	MZ4618	MZPY13	MZPY7.5
MUX_16TO1	MZ4619	MZPY15	MZPY75
MUX_2TO1	MZ4620	MZPY16	MZPY8.2
MUX_4TO1	MZ4621	MZPY18	MZPY82
MUX_8TO1	MZ4622	MZPY20	MZPY9.1
MUX_LATCH	MZ4623	MZPY22	MZPY91
MUX2_1	MZ4624	MZPY24	N2550-6002RB
MUX2_1_INV	MZ4625	MZPY27	N80C196KB
MUX2_1INV_3S	MZ4626	MZPY3.9	N83C196KB
MUX4_1	MZ4627	MZPY30	N87C196KB
MUX4_1_INVO	MZ5520B	MZPY33	NAND13
MUX8_1	MZ5521B	MZPY36	NAND2
MVGSF1N03LT1G	MZ5522B	MZPY39	NAND2
MVMBF0201NLT1G	MZ5523B	MZPY4.3	NAND3

Multisim 14.0 Base Components

NAND3	NCP1117DT25RKG	NCP511SN28T1G	NCV1117ST15T3G
NAND4	NCP1117DT25T5G	NCP511SN30T1G	NCV1117ST18T3G
NAND4	NCP1117DT285G	NCP511SN33T1G	NCV1117ST20T3G
NAND5	NCP1117DT285RKG	NCP511SN50T1G	NCV1117ST25T3G
NAND5	NCP1117DT33G	NCS2001SN1T1G	NCV1117ST33T3G
NAND6	NCP1117DT33RKG	NCS2001SN2T1G	NCV1117ST50T3G
NAND6	NCP1117DT33T5G	NCS2001SQ1T2G	NCV1117STAT3G
NAND7	NCP1117DT50G	NCS2001SQ2T2G	NCV2001SN2T1G
NAND7	NCP1117DT50RKG	NCS2200SN1T1G	NCV2001SQ2T2G
NAND8	NCP1117DTAG	NCS2200SN2T1G	NCV2901DR2G
NAND8	NCP1117DTARKG	NCS2200SQ2T2G	NCV2901DTBR2G
NBRB8H100T4G	NCP1117DTAT5G	NCS2200SQLT1G	NCV2902DR2G
NBRD5H100T4G	NCP1117ST12T3G	NCS2202SN1T1G	NCV2902DTBR2G
NBR52H100T3G	NCP1117ST15T3G	NCS2202SN2T1G	NCV2903DMR2G
NC_CONTACT	NCP1117ST18T3G	NCS2202SQ1T2G	NCV2903DR2G
NCP1117DT12G	NCP1117ST20T3G	NCS2202SQ2T2G	NCV2904DMR2G
NCP1117DT12RKG	NCP1117ST25T3G	NCV1117DT15RKG	NCV2904DR2G
NCP1117DT15G	NCP1117ST285T3G	NCV1117DT18RKG	NCV33074ADTBR2G
NCP1117DT15RKG	NCP1117ST33T3G	NCV1117DT18T5G	NCV33074DR2G
NCP1117DT18G	NCP1117ST50T3G	NCV1117DT20RKG	NCV33272ADR2G
NCP1117DT18RKG	NCP1117STAT3G	NCV1117DT25RKG	NCV833DR2G
NCP1117DT18T5G	NCP511SN15T1G	NCV1117DT33T5G	NDD02N60Z-1G
NCP1117DT20G	NCP511SN18T1G	NCV1117DT50RKG	NDD02N60ZT4G
NCP1117DT20RKG	NCP511SN25T1G	NCV1117DTARKG	NDD03N50Z-1G
NCP1117DT25G	NCP511SN27T1G	NCV1117ST12T3G	

Multisim 14.0 Base Components

NDD03N50ZT4G	NDF10N60ZG	NDS9959	NGB18N40CLBT4G
NDD03N60Z-1G	NDF10N60ZH	NE5532AI	NGB8207NT4G
NDD03N60ZT4G	NDF10N62ZG	NE5532AIP	NGD15N41CLT4G
NDD04N50Z-1G	NDF11N50ZG	NE5532AP	NGD18N40CLBT4G
NDD04N50ZT4G	NDF11N50ZH	NE5532IP	NGD8201NT4G
NDD04N60Z-1G	NDF9406	NE5532P	NHPJ08S600G
NDD04N60ZT4G	NDF9407	NE5534AD	NHPJ15S600G
NDD05N50Z-1G	NDF9409	NE5534AP	NHPV08S600G
NDD05N50ZT4G	NDF9410	NE5534D	NHPV15S600G
NDF02N60ZG	NDS8852H	NE5534P	NI_2VHDCI_68_68_
NDF02N60ZH	NDS8858H	NET_10	RA
NDF03N60ZG	NDS8936	NET_12	NI_50MIL_68_RA
NDF03N60ZH	NDS8947	NET_14	NI_50MIL_68_V
NDF04N60ZG	NDS9936	NET_16	NI_cRIO_4LED_RA
NDF04N60ZH	NDS9942	NET_18	NI_cRIO_BNC
NDF04N62ZG	NDS9943	NET_2	NI_cRIO_DSUB25M
NDF05N50ZG	NDS9947	NET_20	NI_cRIO_DSUB37M
NDF05N50ZH	NDS9948	NET_3	NI_cRIO_INTERFAC
NDF06N60ZG	NDS9952	NET_4	E_GENERIC
NDF06N60ZH	NDS9952A	NET_6	NI_cRIO_INTERFAC
NDF06N62ZG	NDS9953	NET_8	E_ID
NDF08N50ZG	NDS9953A	NF5101	NI_cRIO_INTERFAC
NDF08N50ZH	NDS9955	NF5102	E_PARALLEL
NDF08N60ZG	NDS9956A	NF5103	NI_cRIO_INTERFAC
NDF08N60ZH	NDS9958	NF5301	E_SPI
			NI_cRIO_INTERFAC
			E_USER

Multisim 14.0 Base Components

NI_cRIO_SCREWTERM10	NI-9683_DO	NI-PCI-6013	NI-PCI-6224
NI_sbRIO_J5_CONN	NI-9683_HALFBRIDGE_DO	NI-PCI-6014	NI-PCI-6225
NI_sbRIO_J6_CONN	NI-9683_LVTTL	NI-PCI-6023E	NI-PCI-6229
NI_sbRIO_J7_CONN	NI-AT-GPIB/TNT	NI-PCI-6024E	NI-PCI-6230
NI_sbRIO_J7_PORTS	NID9N05CLT4G	NI-PCI-6030E	NI-PCI-6232
NI_sbRIO_P2_CONNS	NI-DAQCard-6024E	NI-PCI-6032E	NI-PCI-6233
NI_sbRIO_P2_PORTS	NI-DAQCard-6036E	NI-PCI-6034E	NI-PCI-6236
NI_sbRIO_P2_PORTS	NI-DAQCard-6062E	NI-PCI-6035E	NI-PCI-6238
NI_sbRIO_P3_CONNS	NI-DAQCard-6062E	NI-PCI-6036E	NI-PCI-6239
NI_sbRIO_P3_PORTS	NI-DAQPad-6015(Mass.Term.)	NI-PCI-6040E	NI-PCI-6250
NI_sbRIO_P3_PORTS	NI-DAQPad-6020E	NI-PCI-6052E	NI-PCI-6254
NI_sbRIO_P4_CONNS	NI-DAQPad-6052E	NI-PCI-6070E	NI-PCI-6255
NI_sbRIO_P4_PORTS	NI-DAQPad-6052E	NI-PCI-6110	NI-PCI-6259
NI_sbRIO_P4_PORTS	NI-ExpressCard-GPIB	NI-PCI-6111	NI-PCI-6280
NI_sbRIO_P4_PORTS	NIF9N05CLT1G	NI-PCI-6115	NI-PCI-6281
NI_sbRIO_P5_CONNS	NIF9N05CLT3G	NI-PCI-6120	NI-PCI-6284
NI_sbRIO_P5_CONNS	NI-GPIB-ENET/100	NI-PCI-6122	NI-PCI-6289
NI_sbRIO_P5_PORTS	NI-GPIB-ENET/1000	NI-PCI-6123	NI-PCI-7811R
NI_VHDCI_68_RA	NI-GPIB-PCII/IIA	NI-PCI-6132	NI-PCI-7813R
NI_VHDCI_68_V	NI-GPIB-RS232	NI-PCI-6133	NI-PCI-7830R_RMIO
NI-78xxR_RDIO	NI-GPIB-RS485/422	NI-PCI-6143	NI-PCI-7831R_RMIO
NI-9683_AI	NI-GPIB-USB-HS	NI-PCI-6154	NI-PCI-7831R_RMIO
NI-9683_AIO	NI-myDAQ	NI-PCI-6220	NI-PCI-7833R_RMIO
NI-9683_DI	NI-PCI-6011E	NI-PCI-6221	NI-PCI-8232
		NI-PCI-6221(37-Pin)	

Multisim 14.0 Base Components

NI-PCle-6251	NI-PCMCIA-GPIB	NI-PXI-6254	NI-PXIe-6366
NI-PCle-6259	NI-PMC-GPIB	NI-PXI-6255	NI-PXIe-6368
NI-PCle-6320	NI-PXI-6030E	NI-PXI-6259	NI-PXI-GPIB
NI-PCle-6321	NI-PXI-6040E	NI-PXI-6280	NI-sbRIO-9605
NI-PCle-6323	NI-PXI-6052E	NI-PXI-6281	NI-sbRIO-9606
NI-PCle-6341	NI-PXI-6070E	NI-PXI-6284	NI-sbRIO-9651
NI-PCle-6343	NI-PXI-6115	NI-PXI-6289	NI-SCXI-1127_1-Wire
NI-PCle-6351	NI-PXI-6120	NI-PXI-7811R	NI-SCXI-1127_2-Wire
NI-PCle-6353	NI-PXI-6122	NI-PXI-7813R	NI-SCXI-1127_4-Wire
NI-PCle-6361	NI-PXI-6123	NI-PXI-7830R_RMIO	NI-SCXI-1127_4-Wire
NI-PCle-6363	NI-PXI-6132	NI-PXI-7831R_RMIO	NI-SCXI-1127_Independent
NI-PCle-7841R_RMIO	NI-PXI-6133	NI-PXI-7833R_RMIO	NI-SCXI-1127_Matrix
NI-PCle-7842R_RMIO	NI-PXI-6143	NI-PXI-7841R_RMIO	NI-SCXI-1128_1-Wire
NI-PCle-7851R_RMIO	NI-PXI-6221	NI-PXI-7842R_RMIO	NI-SCXI-1128_2-Wire
NI-PCle-7852R_RMIO	NI-PXI-6224	NI-PXI-7851R_RMIO	NI-SCXI-1128_4-Wire
NI-PCle-GPIB	NI-PXI-6225	NI-PXI-7852R_RMIO	NI-SCXI-1128_Independent
NI-PCle-GPIB/LP	NI-PXI-6229	NI-PXI-7853R_RMIO	NI-SCXI-1128_Matrix
NI-PCle-GPIB+	NI-PXI-6230	NI-PXI-7854R_RMIO	NI-SCXI-1160
NI-PCle-GPIB+/LP	NI-PXI-6232	NI-PXI-8232	NI-SCXI-1163R
NI-PCI-GPIB	NI-PXI-6233	NI-PXIe-6124	
NI-PCI-GPIB/LP	NI-PXI-6236	NI-PXIe-6341	
NI-PCI-GPIB+	NI-PXI-6238	NI-PXIe-6356	
	NI-PXI-6239	NI-PXIe-6358	
	NI-PXI-6250	NI-PXIe-6361	
	NI-PXI-6251	NI-PXIe-6363	

Multisim 14.0 Base Components

NI-USB-6212(Mass.Term.)	NJL0302DG	NJM072L	NJM2043L
	NJL1302DG	NJM072M	NJM2043M
NI-USB-6216(Mass.Term.)	NJL3281DG	NJM074D	NJM2058D
	NJL4281D	NJM074M	NJM2058M
NI-USB-6225(Mass.Term.)	NJL4281DG	NJM074V	NJM2059D
	NJL4302D	NJM082BD	NJM2059M
NI-USB-6251(Mass.Term.)	NJL4302DG	NJM082BL	NJM2060D
	NJM022BD	NJM082BM	NJM2060M
NI-USB-6259(Mass.Term.)	NJM022BL	NJM082BV	NJM2068D
	NJM022BM	NJM082D	NJM2068L
NI-USB-6281(Mass.Term.)	NJM022D	NJM082L	NJM2068M
	NJM022L	NJM082V	NJM2082D
NI-USB-6289(Mass.Term.)	NJM022M	NJM084D	NJM2082L
	NJM062D	NJM084M	NJM2082M
NI-USB-7845R_MIO	NJM062L	NJM084V	NJM2097M
NI-USB-7846R_MIO	NJM062M	NJM13600D	NJM2100D
NI-USB-7855R_MIO	NJM062V	NJM13600M	NJM2100L
NI-USB-7856R_MIO	NJM064D	NJM13700D	NJM2100M
NI-USB-78xxR_DIO	NJM064M	NJM13700M	NJM2100V
NJD1718T4G	NJM064V	NJM1458D	NJM2107F
NJD2873T4G	NJM072BD	NJM1458M	NJM2114D
NJD35N04G	NJM072BL	NJM2041D	NJM2114L
NJD35N04T4G	NJM072BM	NJM2041L	NJM2115D
NJL0281D	NJM072BV	NJM2041M	NJM2115L
NJL0281DG	NJM072D	NJM2043D	NJM2115M
NJL0302D			

Multisim 14.0 Base Components

NJM2120D	NJM3414D	NJM5534D	NJVMJD3055T4G
NJM2120L	NJM3414L	NJM5534M	NJVMJD31T4G
NJM2120M	NJM3414M	NJM741D	NJVMJD32CG
NJM2121D	NJM3415D	NJM741E	NJVMJD32CT4G
NJM2121L	NJM3415L	NJM741M	NJVMJD32T4G
NJM2121M	NJM3415M	NJMOP-07D	NJVMJD350T4G
NJM2900M	NJM3416V	NJMOP-07M	NJVMJD42CRLG
NJM2900N	NJM353D	NJT4030PT1G	NJVMJD42CT4G
NJM2902M	NJM353M	NJT4030PT3G	NJVMJD44E3T4G
NJM2902N	NJM3900M	NJT4031NT1G	NJVMJD44H11G
NJM2902V	NJM3900N	NJT4031NT3G	NJVMJD44H11RLG
NJM2904D	NJM4250D	NJV4030PT1G	NJVMJD44H11T4G
NJM2904L	NJM4250M	NJV4030PT3G	NJVMJD45H11RLG
NJM2904M	NJM4565D	NJV4031NT1G	NJVMJD45H11T4G
NJM2904V	NJM4565L	NJV4031NT3G	NJVMJD50T4G
NJM318D	NJM4565M	NJVMJB41CT4G	NJVMJD6039T4G
NJM318M	NJM4565V	NJVMJB42CT4G	NJVNJD2873T4G
NJM324D	NJM4580D	NJVMJB44H11T4G	NJVNJD35N04G
NJM324M	NJM4580E	NJVMJB45H11T4G	NJVNJD35N04T4G
NJM3403AD	NJM4580L	NJVMJD112T4G	NJW0281G
NJM3403AM	NJM4741D	NJVMJD117T4G	NJW0302G
NJM3403AV	NJM4741M	NJVMJD210T4G	NJW1302G
NJM3404AD	NJM5532D	NJVMJD243T4G	NJW21193G
NJM3404AL	NJM5532L	NJVMJD253T4G	NJW21194G
NJM3404AM	NJM5532M	NJVMJD2955T4G	NJW3281G

Multisim 14.0 Base Components

NJX1675PDR2G	NPD8301	NRVB2045EMFST1G	NRVB8H100MFST3G
NLT_VIRTUAL	NPD8303	NRVB2045EMFST3G	NRVBA130LT3G
NMOSFET_Thermal	NRVA4004T3G	NRVB2H100SFT3G	NRVBA160T3G
NO_CONTACT	NRVB0530T1G	NRVB30H100MFST1G	NRVBA1H100T3G
NON_IDEAL_BATTERY	NRVB0530T3G	NRVB30H100MFST3G	NRVBA210LT3G
NONLINEAR_DEPENDENT	NRVB0540T1G	NRVB30H100MFST1G	NRVBA2H100T3G
NOR2	NRVB0540T3G	NRVB440MFST1G	NRVBA340T3G
NOR2	NRVB10100G	NRVB440MFST3G	NRVBB1060T4G
NOR3	NRVB10100MFST1G	NRVB440MFSWFT1G	NRVBB20100CTT4G
NOR3	NRVB10100MFST3G	NRVB440MFSWFT3G	NRVBB2060CTT4G
NOR4	NRVB1045MFST1G	NRVB460MFST1G	NRVBB20H100CTT4G
NOR4	NRVB1045MFST3G	NRVB5100MFST1G	NRVBB2535CTLG
NOR5	NRVB120ESFT1G	NRVB5100MFST3G	NRVBB2535CTLT4G
NOR5	NRVB120ESFT3G	NRVB540MFST1G	NRVBB3030CTLG
NOR6	NRVB120LSFT1G	NRVB540MFST3G	NRVBB3030CTLT4G
NOR6	NRVB1240MFST1G	NRVB560MFST1G	NRVBB30H60CTT4G
NOR7	NRVB1240MFST3G	NRVB560MFST3G	NRVBB4030T4G
NOR7	NRVB130T1G	NRVB560MFST1G	NRVBB41H100CTT4G
NOR8	NRVB140ESFT1G	NRVB5H100MFST1G	NRVBS20100CTT4G
NOR8	NRVB140ESFT3G	NRVB8H100MFST1G	NRVBD1035CTLT4G
NOT	NRVB140SFT1G		NRVBD640CTG
NPD5564	NRVB140SFT3G		NRVBD640CTT4G
NPD5565	NRVB1H100SFT3G		
NPD5566			

Multisim 14.0 Base Components

NRVBD650CTT4G	NRVUB1660CTT4G	NSBA115TDP6T5G	NSBC114EDXV6T5G
NRVBD660CTG	NRVUD550PFT4G	NSBA115TF3T5G	NSBC114EF3T5G
NRVBD660CTT4G	NRVUD620CTG	NSBA123EF3T5G	NSBC114EPDP6T5G
NRVBM110ET1G	NRVUD620CTT4G	NSBA123JDP6T5G	NSBC114EPDXV6T1 G
NRVBM110LT1G	NRVUS230T3G	NSBA123JDXV6T5G	NSBC114EPDXV6T5 G
NRVBM110LT3G	NRVUS240T3G	NSBA123JF3T5G	NSBC114TDP6T5G
NRVBM120ET1G	NS32FV16-20	NSBA123TDP6T5G	NSBC114TDXV6T1G
NRVBM120ET3G	NS32FV16-25	NSBA123TF3T5G	NSBC114TF3T5G
NRVBM130LT1G	NS32FX161-15	NSBA124EDP6T5G	NSBC114YDP6T5G
NRVBM130LT3G	NS32FX161-20	NSBA124EF3T5G	NSBC114YDXV6T1G
NRVBM140T1G	NS32FX164-20	NSBA124XF3T5G	NSBC114YDXV6T5G
NRVBM140T3G	NS32FX164-25	NSBA143EDP6T5G	NSBC114YF3T5G
NRVBS2040LT3G	NSA5.0AT3G	NSBA143EF3T5G	NSBC114YPDP6T5G
NRVBS240LT3G	NSB12ANT3G	NSBA143TF3T5G	NSBC114YPDXV6T1 G
NRVBS260T3G	NSB4904DW1T1G	NSBA143ZDP6T5G	NSBC114YPDXV6T5 G
NRVBS3100T3G	NSB8MT-E3/81	NSBA143ZF3T5G	NSBC115EDXV6T1G
NRVBS3200T3G	NSB9435T1G	NSBA144EDP6T5G	NSBC115TDP6T5G
NRVBS3201T3G	NSBA114EDP6T5G	NSBA144EDXV6T1G	NSBC115TF3T5G
NRVBS330T3G	NSBA114EDXV6T1G	NSBA144EF3T5G	NSBC115TPDP6T5G
NRVBS360T3G	NSBA114EF3T5G	NSBA144TF3T5G	NSBC123EF3T5G
NRVBS4201T3G	NSBA114TDP6T5G	NSBA144WDP6T5G	NSBC123JDP6T5G
NRVBS540T3G	NSBA114TF3T5G	NSBA144WF3T5G	NSBC123JF3T5G
NRVS1504T3G	NSBA114YDP6T5G	NSBC113EF3T5G	NSBC114EDP6T5G
NRVUB1620CTRT4G	NSBA114YDXV6T1G	NSBC114EDP6T5G	NSBC114EDXV6T1G
NRVUB1620CTT4G	NSBA115EDXV6T1G	NSBC114EDXV6T1G	

Multisim 14.0 Base Components

NSBC123JPDP6T5G	NSBC144EPDP6T5G	NSR0320MW2T1G	NSS12200WT1G
NSBC123JPDXV6T1 G	NSBC144EPDXV6T1 G	NSR0320MW2T3G	NSS12201LT1G
NSBC123TDP6T5G	NSBC144TF3T5G	NSR0320XV6T1G	NSS12500UW3T2G
NSBC123TF3T5G	NSBC144WDP6T5G	NSR0320XV6T5G	NSS12501UW3T2G
NSBC124EDP6T5G	NSBC144WF3T5G	NSR0340HT1G	NSS12601CF8T1G
NSBC124EDXV6T1G	NSD16F3T5G	NSR0340P2T5G	NSS1C200LT1G
NSBC124EF3T5G	NSD914F3T5G	NSR0340V2T1G	NSS1C200MZ4T1G
NSBC124EPDXV6T1 G	NSDEMP11XV6T1G	NSR0520V2T1G	NSS1C200MZ4T3G
NSBC124XF3T5G	NSDEMP11XV6T5G	NSR05F20NXT5G	NSS1C201LT1G
NSBC143EDP6T5G	NSL12AWT1G	NSR05F30NXT5G	NSS1C201MZ4T1G
NSBC143EF3T5G	NSM80100MT1G	NSR05F40NXT5G	NSS1C201MZ4T3G
NSBC143TF3T5G	NSM80101MT1G	NSR0620P2T5G	NSS1C300ET4G
NSBC143TPDXV6T1 G	NSR0130P2T5G	NSR1020MW2T1G	NSS1C301ET4G
NSBC143ZDP6T5G	NSR0140P2T5G	NSR1020MW2T3G	NSS20200LT1G
NSBC143ZDXV6T1G	NSR01F30MXT5G	NSR10F20NXT5G	NSS20201LT1G
NSBC143ZF3T5G	NSR01F30NXT5G	NSR10F30NXT5G	NSS20300MR6T1G
NSBC143ZPDP6T5G	NSR01L30MXT5G	NSR10F40NXT5G	NSS20500UW3T2G
NSBC143ZPDV6T1 G	NSR01L30NXT5G	NSR20F20NXT5G	NSS20501UW3T2G
NSBC144EDP6T5G	NSR0230P2T5G	NSR20F30NXT5G	NSS20601CF8T1G
NSBC144EDXV6T1G	NSR0240HT1G	NSR30CM3T5G	NSS30100LT1G
NSBC144EDXV6T5G	NSR0240P2T5G	NSRLV20MW2T1G	NSS30101LT1G
NSBC144EF3T5G	NSR0240V2T1G	NSS12100M3T5G	NSS30201MR6T1G
	NSR02F30NXT5G	NSS12100UW3TCG	NSS35200CF8T1G
	NSR02L30NXT5G	NSS12100XV6T1G	NSS35200MR6T1G
		NSS12200LT1G	NSS40200LT1G

Multisim 14.0 Base Components

NSS40200UW6T1G	NST846BF3T5G	NSVB144EPDXV6T1G	NSVT30010MXV6T1G
NSS40201LT1G	NST847BF3T5G		
NSS40300DDR2G	NST848BF3T5G	NSVBA114YDXV6T1G	NSVT3904DXV6T1G
NSS40300MDR2G	NST856BF3T5G	NSVBAT54WT1G	NTA4001NT1G
NSS40300MZ4T1G	NST857BF3T5G	NSVBAV70TT1G	NTA4151PT1G
NSS40301MDR2G	NSTB1005DXV5T1G	NSVBAV70TT3G	NTA4153NT1G
NSS40301MZ4T1G	NSTR4501NT1G	NSVBC124EDXV6T1G	NTA7002NT1G
NSS40302PDR2G	NSV1C300ET4G		NTB25P06T4G
NSS40500UW3T2G	NSV1C301ET4G	NSVBCP69T1G	NTB30N06LT4G
NSS40501UW3T2G	NSV20200LT1G	NSVMMBD353LT1G	NTB30N20T4G
NSS40600CF8T1G	NSV20201LT1G	NSVMMBT589LT1G	NTB45N06LT4G
NSS40601CF8T1G	NSV40200LT1G	NSVMMBTH10LT1G	NTB45N06T4G
NSS60200LT1G	NSV40201LT1G	NSVMMUN2132LT1G	NTB5404NT4G
NSS60201LT1G	NSV40300MDR2G		NTB5405NT4G
NSS60600MZ4T1G	NSV40300MZ4T1G	NSVMMUN2232LT1G	NTB5605PT4G
NSS60601MZ4T1G	NSV40301MZ4T1G	NSVMUN2212T1G	NTB60N06T4G
NST30010MXV6T1G	NSV60600MZ4T1G	NSVMUN2233T1G	NTB6410ANG
	NSV60600MZ4T3G	NSVMUN5131T1G	NTB6410ANT4G
NST3904DXV6T1G	NSV60601MZ4T1G	NSVMUN5132T1G	NTB6411ANG
NST3904DXV6T5G	NSV60601MZ4T3G	NSVMUN5212DW1T1G	NTB6411ANT4G
NST3904F3T5G	NSV9435T1G		NTB6412ANG
NST3906DXV6T1G	NSVB123JPDXV6T1G	NSVMUN5333DW1T1G	NTB6412ANT4G
NST3906F3T5G			NTB6413ANG
NST3946DXV6T1G	NSVB143ZPDXV6T1G	NSVMUN5334DW1T1G	NTB6413ANT4G
NST3946DXV6T5G			NTB75N03L09T4G

Multisim 14.0 Base Components

NTB75N06T4G	NTD40N03RT4G	NTD4857NT4G	NTD4913N-1G
NTBV5605T4G	NTD4302T4G	NTD4858N-35G	NTD4913N-35G
NTD110N02RT4G	NTD4804NT4G	NTD4858NT4G	NTD4913NT4G
NTD12N10-1G	NTD4805N-1G	NTD4860N-35G	NTD4960N-1G
NTD12N10T4G	NTD4805NT4G	NTD4860NT4G	NTD4960N-35G
NTD14N03RT4G	NTD4806N-35G	NTD4863N-35G	NTD4960NT4G
NTD18N06LT4G	NTD4806NT4G	NTD4863NAT4G	NTD4963N-1G
NTD18N06T4G	NTD4808N-1G	NTD4863NT4G	NTD4963N-35G
NTD20N03L27T4G	NTD4808NT4G	NTD4863NT4H	NTD4963NT4G
NTD20N06T4G	NTD4809N-35G	NTD4865NT4G	NTD4965N-1G
NTD20P06LG	NTD4809NH-1G	NTD4904N-1G	NTD4965N-35G
NTD20P06LT4G	NTD4809NH-35G	NTD4904N-35G	NTD4965NT4G
NTD24N06LT4G	NTD4809NHT4G	NTD4904NT4G	NTD4969N-1G
NTD24N06T4G	NTD4809NT4G	NTD4905N-1G	NTD4969N-35G
NTD2955-1G	NTD4810N-35G	NTD4905N-35G	NTD4969NT4G
NTD2955G	NTD4810NT4G	NTD4905NT4G	NTD4970N-1G
NTD2955T4G	NTD4813N-35G	NTD4906N-1G	NTD4970N-35G
NTD3055-094-1G	NTD4813NH-1G	NTD4906N-35G	NTD4970NT4G
NTD3055-094T4G	NTD4813NH-35G	NTD4906NT4G	NTD5406NT4G
NTD3055-150T4G	NTD4813NHT4G	NTD4909N-1G	NTD5407NT4G
NTD3055L104-1G	NTD4813NT4G	NTD4909N-35G	NTD5802NT4G
NTD3055L104G	NTD4815N-35G	NTD4909NT4G	NTD5803NT4G
NTD3055L104T4G	NTD4815NT4G	NTD4910N-1G	NTD5804NT4G
NTD3055L170T4G	NTD4855NT4G	NTD4910N-35G	NTD5805NT4G
NTD32N06LT4G	NTD4856NT4G	NTD4910NT4G	NTD5806NT4G

Multisim 14.0 Base Components

NTD5807NT4G	NTF6P02T3G	NTHS4166NT1G	NTLGD3502NT2G
NTD5865NL-1G	NTGD1100LT1G	NTHS5404T1G	NTLGF3402PT2G
NTD5865NLT4G	NTGD3149CT1G	NTHS5441T1G	NTLJD3115PT1G
NTD5867NL-1G	NTGD4161PT1G	NTHS5443T1G	NTLJD3119CTAG
NTD5867NLT4G	NTGD4167CT1G	NTJD1155LT1G	NTLJD3119CTBG
NTD6414AN-1G	NTGS3130NT1G	NTJD4001NT1G	NTLJD4116NT1G
NTD6414ANT4G	NTGS3136PT1G	NTJD4105CT1G	NTLJF3117PT1G
NTD6415AN-1G	NTGS3441PT1G	NTJD4105CT2G	NTLJF4156NT1G
NTD6415ANT4G	NTGS3441T1G	NTJD4152PT1G	NTLJF4156NTAG
NTD6416AN-1G	NTGS3443T1G	NTJD4158CT1G	NTLJS2103PTBG
NTD6416ANL-1G	NTGS3446T1G	NTJD4158CT2G	NTLJS3113PT1G
NTD6416ANLT4G	NTGS4111PT1G	NTJD4401NT1G	NTLJS3113PTAG
NTD6416ANT4G	NTGS4141NT1G	NTJD5121NT1G	NTLJS4114NT1G
NTD6600NT4G	NTGS5120PT1G	NTJD5121NT2G	NTLUD3A260PZTAG
NTD70N03R-1G	NTHC5513T1G	NTJS3151PT1G	NTLUD3A260PZTBG
NTD70N03RT4G	NTHD2102PT1G	NTJS3157NT1G	NTLUF4189NZTAG
NTDV20N06T4G	NTHD3100CT1G	NTJS4151PT1G	NTLUS3A40PZTAG
NTE4151PT1G	NTHD3101FT1G	NTJS4160NT1G	NTLUS3A40PZTBG
NTE4153NT1G	NTHD3102CT1G	NTJS4405NT1G	NTLUS3A90PZTAG
NTF2955T1G	NTHD3133PFT1G	NTK3043NT1G	NTLUS3A90PZTBG
NTF3055-100T1G	NTHD4102PT1G	NTK3134NT1G	NTMD3P03R2G
NTF3055-100T3G	NTHD4502NT1G	NTK3134NT5G	NTMD4184PFR2G
NTF3055L108T1G	NTHD4508NT1G	NTK3139PT1G	NTMD4820NR2G
NTF3055L175T1G	NTHD4P02FT1G	NTK3139PT5G	NTMD4840NR2G
NTF5P03T3G	NTHS4101PT1G	NTK3142PT1G	NTMD4884NFR2G

Multisim 14.0 Base Components

NTMD4N03R2G	NTMFS4847NAT3G	NTMFS4927NT1G	NTMS4807NR2G
NTMD5836NLR2G	NTMFS4847NT1G	NTMFS4927NT3G	NTMS4816NR2G
NTMD5838NLR2G	NTMFS4851NT1G	NTMFS4934NT1G	NTMS4840NR2G
NTMD6N02R2G	NTMFS4852NT1G	NTMFS4934NT3G	NTMS4872NR2G
NTMD6P02R2G	NTMFS4852NT3G	NTMFS4935NT1G	NTMS4873NFR2G
NTMFS4108NT1G	NTMFS4897NFT1G	NTMFS4935NT3G	NTMS4916NR2G
NTMFS4119NT1G	NTMFS4897NFT3G	NTMFS4936NT1G	NTMS4917NR2G
NTMFS4744NT1G	NTMFS4898NFT1G	NTMFS4936NT3G	NTMS4920NR2G
NTMFS4821NT1G	NTMFS4898NFT3G	NTMFS4937NT1G	NTMS4935NR2G
NTMFS4823NT1G	NTMFS4899NFT1G	NTMFS4937NT3G	NTMS4937NR2G
NTMFS4823NT3G	NTMFS4899NFT3G	NTMFS4939NT1G	NTMS4939NR2G
NTMFS4825NFET1G	NTMFS4921NT1G	NTMFS4939NT3G	NTMS5835NLR2G
NTMFS4825NFET3G	NTMFS4921NT3G	NTMFS4941NT1G	NTMS5838NLR2G
NTMFS4833NT1G	NTMFS4922NET1G	NTMFS4941NT3G	NTMS5P02R2G
NTMFS4833NT3G	NTMFS4922NET3G	NTMFS4943NT1G	NTNS3A65PZT5G
NTMFS4834NT1G	NTMFS4923NET1G	NTMFS4943NT3G	NTNUS3171PZT5G
NTMFS4835NT1G	NTMFS4923NET3G	NTMFS4945NT1G	NTP2955G
NTMFS4836NT1G	NTMFS4925NET1G	NTMFS5830NLT1G	NTP35N15G
NTMFS4837NHT1G	NTMFS4925NET3G	NTMS10P02R2G	NTR0202PLT1G
NTMFS4839NHT1G	NTMFS4925NT1G	NTMS4176PR2G	NTR1P02LT1G
NTMFS4841NHT1G	NTMFS4925NT3G	NTMS4177PR2G	NTR1P02LT3G
NTMFS4841NT1G	NTMFS4926NET1G	NTMS4503NR2G	NTR2101PT1G
NTMFS4845NT1G	NTMFS4926NET3G	NTMS4800NR2G	NTR3161NT1G
NTMFS4846NT1G	NTMFS4926NT1G	NTMS4801NR2G	NTR3162PT1G
NTMFS4847NAT1G	NTMFS4926NT3G	NTMS4802NR2G	NTR4003NT1G

Multisim 14.0 Base Components

NTR4003NT3G	NTST20120CTG	NTTFS4937NTAG	NTZS3151PT1G
NTR4101PT1G	NTST20U100CTG	NTTFS4937NTWG	NUP1105LT1G
NTR4170NT1G	NTST30100CTG	NTTFS4939NTAG	NUP1301
NTR4171PT1G	NTST30100CTH	NTTFS4939NTWG	NUP1301ML3T1G
NTR4501NT1G	NTST30100SG	NTTFS4941NTAG	NUP1301U
NTR4502PT1G	NTST30120CTG	NTTFS4941NTWG	NUP2105LT1G
NTR4502PT3G	NTST30U100CTG	NTTFS4943NTAG	NUP2202W1T2G
NTR4503NT1G	NTST30U100CTH	NTTFS4945NTAG	NUP4102XV6T1G
NTS2101PT1G	NTST40120CTG	NTTFS5811NLTAG	NUP4103FCT1G
NTS4001NT1G	NTST40120CTH	NTTFS5811NLTWG	NUP4201DR2G
NTS4101PT1G	NTSV20100CTG	NTTFS5820NLTAG	NUP4201MR6T1G
NTS4173PT1G	NTSV20120CTG	NTTFS5820NLTWG	NUP4202W1T2G
NTS4409NT1G	NTSV20U100CTG	NTUD3127CT5G	NUP4301MR6T1G
NTSB20100CT-1G	NTSV30100CTG	NTUD3128NT5G	NUP4302MR6T1G
NTSB20U100CT-1G	NTSV30120CTG	NTUD3169CZT5G	NUP4304MR6T1G
NTSB30100CT-1G	NTTD4401FR2G	NTUD3170NZT5G	NUP45V6P5T5G
NTSB30100S-1G	NTTFS4800NTAG	NTUD3171PZT5G	NUS3116MTR2G
NTSB30U100CT-1G	NTTFS4821NTAG	NTZD3152PT1G	NVB6413ANT4G
NTSJ20100CTG	NTTFS4821NTWG	NTZD3154NT1G	NVD4804NT4G
NTSJ2080CTG	NTTFS4823NTAG	NTZD3154NT2G	NVD5117PLT4G
NTSJ20U100CTG	NTTFS4823NTWG	NTZD3154NT5G	NVD5802NT4G
NTSJ30100CTG	NTTFS4824NTAG	NTZD3155CT1G	NVD5807NT4G
NTSJ3080CTG	NTTFS4840NTAG	NTZD3155CT2G	NVD5865NLT4G
NTSJ30U80CTG	NTTFS4932NTAG	NTZD3155CT5G	NVD5890NT4G
NTST20100CTG	NTTFS4932NTWG	NTZD5110NT1G	NVDD5894NLT4G

Multisim 14.0 Base Components

NVF2955T1G	NX3008PBK	NZH24C	NZX10C
NVF3055-100T1G	NX3008PBKMB	NZH27C	NZX11A
NVF3055L108T1G	NX3008PBKS	NZH30C	NZX11C
NVF3055L108T3G	NX3008PBKT	NZH3V0B	NZX11D
NVF5P03T3G	NX3008PBKV	NZH3V3A	NZX12A
NVF6P02T3G	NX3008PBKW	NZH3V6B	NZX12B
NVMD3P03R2G	NX7002AK	NZH3V9B	NZX12C
NVMS4816NR2G	NX7002AKS	NZH4V3B	NZX12D
NVTA7002NT1G	NX7002AKW	NZH4V7B	NZX13B
NVTFS4824NTAG	NXP3875G	NZH5V1B	NZX13C
NVTFS4824NTWG	NXP3875Y	NZH5V6B	NZX14A
NVTFS5826NLTAG	NZ9F2V4ST5G	NZH6V2B	NZX14B
NVTFS5826NLTWG	NZ9F2V4T5G	NZH6V8B	NZX14C
NVTJD4001NT1G	NZ9F2V7ST5G	NZH7V5C	NZX15B
NVTR01P02LT1G	NZ9F5V1T5G	NZH8V2B	NZX16A
NVTR0202PLT1G	NZ9F6V2ST5G	NZH9V1B	NZX16B
NVTR4502PT1G	NZH10C	NZL5V6ATT1G	NZX16C
NVTR4503NT1G	NZH11C	NZL5V6AXV3T1G	NZX18A
NX2301P	NZH12B	NZL6V8AXV3T1G	NZX18B
NX3008NBK	NZH13B	NZL7V5AXV3T1G	NZX18C
NX3008NBKMB	NZH15B	NZQA5V6XV5T1G	NZX20A
NX3008NBKS	NZH16C	NZQA6V8AXV5T1G	NZX20B
NX3008NBKT	NZH18C	NZQA6V8AXV5T2G	NZX22A
NX3008NBKV	NZH20C	NZQA6V8AXV5T3G	NZX22B
NX3008NBKW	NZH22C	NZX10A	NZX24A

Multisim 14.0 Base Components

NZX24B	NZX5V6D	OP02CZ	OP06GZ
NZX27A	NZX5V6E	OP04AK	OP07AH
NZX27B	NZX6V2B	OP04AY	OP07AJ
NZX27C	NZX6V2C	OP04EY	OP07AJ8
NZX2V4A	NZX6V2D	OP05AH	OP07AZ
NZX2V7B	NZX6V2E	OP05AJ	OP07CD
NZX30A	NZX6V8A	OP05AJ8	OP07CH
NZX30C	NZX6V8B	OP05AZ	OP07CJ8
NZX33C	NZX6V8C	OP05CH	OP07CJG
NZX36C	NZX7V5A	OP05CJ	OP07CN8
NZX3V0B	NZX7V5B	OP05CJ8	OP07CP
NZX3V3B	NZX7V5D	OP05CN8	OP07CS8
NZX3V3C	NZX8V2A	OP05CP	OP07DD
NZX3V6C	NZX8V2B	OP05CZ	OP07DJG
NZX3V9C	NZX8V2D	OP05EH	OP07DP
NZX4V3C	NZX9V1B	OP05EJ	OP07ED
NZX4V7A	NZX9V1E	OP05EJ8	OP07EH
NZX4V7C	OCTAL_REG	OP05EN8	OP07EJ8
NZX4V7D	OL	OP05EP	OP07EJG
NZX5V1B	OP01CZ	OP05EZ	OP07EN8
NZX5V1C	OP01J	OP05H	OP07EP
NZX5V1D	OP02AJ	OP05J	OP07H
NZX5V6A	OP02AZ	OP05J8	OP07J
NZX5V6B	OP02CJ	OP06AJ	OP07J8
NZX5V6C	OP02CP	OP06GJ	OP07RC/883

Multisim 14.0 Base Components

OP07Y	OP15BJ/883	OP16AJ	OP177FP
OP07Z	OP15BZ/883	OP16BH	OP177FS
OP08	OP15CH	OP16BJ/883	OP177FZ
OP09AY	OP15EH	OP16BZ/883	OP177GP
OP09BY	OP15EJ	OP16C	OP177GS
OP10AY	OP15EZ	OP16CH	OP177GZ
OP10CY	OP15FH	OP16EH	OP183GP
OP10EY	OP15FJ	OP16EJ	OP183GS
OP10Y	OP15FP	OP16EZ	OP184ES
OP113EP	OP15FZ	OP16FH	OP191GP
OP113ES	OP15GH	OP16FJ	OP191GS
OP113FP	OP15GJ	OP16FP	OP193EP
OP113FS	OP15GN8	OP16FZ	OP193ES
OP1177AR	OP15GP	OP16GH	OP193FP
OP1177ARM	OP15GS	OP16GJ	OP193FS
OP11GP	OP15GZ	OP16GN8	OP196GP
OP11GS	OP160ARC/883	OP16GP	OP196GS
OP12BJ	OP160AZ	OP16GS	OP200AZ
OP12BZ/883	OP160FZ	OP16GZ	OP200EZ
OP12EJ	OP160GP	OP176GP	OP200FZ
OP12EZ	OP160GS	OP176GS	OP200GP
OP15AH	OP162DRU	OP177AZ	OP200GS
OP15AJ	OP162GS	OP177BRC/883	OP207AY
OP15AZ	OP162GSZ	OP177BZ	OP207EY
OP15BH	OP16AH	OP177EZ	OP207FY

Multisim 14.0 Base Components

OP20BJ	OP215CJ/883	OP21FJ	OP227AJ
OP20BZ	OP215CJ8	OP21FP	OP227CJ
OP20CZ	OP215CZ/883	OP21FZ	OP227EJ
OP20FP	OP215EH	OP21GJ	OP227EN
OP20GJ	OP215EJ	OP21GP	OP227GJ
OP20GP	OP215EJ8	OP21HS	OP227GN
OP20GZ	OP215EN8	OP220AJ	OP22AJ/883
OP20HJ	OP215EP	OP220AZ	OP22AZ
OP20HS	OP215EZ	OP220CJ	OP22HP
OP20HZ	OP215FJ	OP220CZ	OP22HS
OP213AZ/883	OP215FP	OP220EZ	OP22HZ
OP213BZ/883	OP215FZ	OP220FZ	OP237AJ
OP213EP	OP215GH	OP220GJ	OP237CJ
OP213ES	OP215GJ8	OP220GP	OP237EJ
OP213EZ	OP215GN8	OP220GS	OP237EN
OP213FP	OP215GP	OP220GZ	OP237GJ
OP213FS	OP215GS	OP221AJ/883	OP237GN
OP215AH	OP215GZ	OP221AZ	OP249AJ
OP215AJ	OP2177AR	OP221BJ	OP249ARC/883
OP215AJ8	OP2177ARM	OP221CJ	OP249AZ
OP215AZ	OP2177ARMZ	OP221EZ	OP249EJ
OP215BJ/883	OP2177ARZ	OP221GJ	OP249FJ
OP215BRC/883	OP21AJ	OP221GP	OP249FZ
OP215BZ/883	OP21AZ	OP221GS	OP249GP
OP215CH	OP21EZ	OP221GZ	OP249GS

Multisim 14.0 Base Components

OP260AJ	OP27BR/883	OP27GSZ	OP293EP
OP260ARC/883	OP27BZ	OP27GZ	OP293ES
OP260GP	OP27CH	OP281GRU	OP293FP
OP260GS	OP27CJ	OP281GS	OP293FS
OP262DRU	OP27CJ8	OP282AZ/883	OP295A
OP262DRUZ-REEL	OP27CJG	OP282GP	OP295AP
OP262GS	OP27CZ	OP282GS	OP295GP
OP262GSZ	OP27EH	OP283GP	OP295GS
OP262HRUZ-REEL	OP27EJ	OP283GS	OP296GP
OP270EZ	OP27EJ8	OP284EP	OP296GS
OP270FZ	OP27EN8	OP284ES	OP296HRU
OP270GP	OP27EP	OP284FP	OP297ARC/883
OP270GS	OP27EPZ	OP284FS	OP297AZ
OP275GP	OP27EZ	OP285GP	OP297AZ/883
OP275GS	OP27FJ	OP285GS	OP297EZ
OP279GP	OP27FP	OP290ARC/883	OP297FP
OP279GS	OP27FZ	OP290AZ	OP297FZ
OP279HRU	OP27GH	OP290EZ	OP297GP
OP27AH	OP27GJ	OP290FZ	OP297GS
OP27AJ	OP27GJ8	OP290GP	OP32AZ
OP27AJ8	OP27GJZ	OP290GS	OP32EP
OP27AJG	OP27GN8	OP291GP	OP32EZ
OP27AL	OP27GP	OP291GS	OP32FP
OP27AZ	OP27GPZ	OP292GP	OP32FZ
OP27BJ	OP27GS	OP292GS	OP32GP

Multisim 14.0 Base Components

OP32GZ	OP37GH	OP41BJ	OP42ARC/883
OP37AFK	OP37GJ	OP41EJ	OP42AZ
OP37AH	OP37GJ8	OP41FJ	OP42EJ
OP37AJ	OP37GN8	OP41GP	OP42EZ
OP37AJ8	OP37GP	OP41GS	OP42FJ
OP37AJG	OP37GS	OP420BY	OP42FZ
OP37AL	OP37GZ	OP420CRC/883	OP42GP
OP37AZ	OP400ATC/883	OP420CY	OP42GS
OP37BJ	OP400AY	OP420FY	OP43
OP37BRC/883	OP400EY	OP420GP	OP43A
OP37BZ	OP400FY	OP420GS	OP43B
OP37CH	OP400GP	OP420GY	OP43E
OP37CJ	OP400GS	OP420HP	OP43F
OP37CJ8	OP400HP	OP420HS	OP43G
OP37CJG	OP400HS	OP420HY	OP44AJ
OP37CZ	OP413EP	OP421BY	OP462DRU
OP37EH	OP413ES	OP421CY	OP462DRUZ-REEL
OP37EJ	OP413EY	OP421FY	OP462DS
OP37EJ8	OP413FP	OP421GP	OP462GS
OP37EN8	OP413FS	OP421GS	OP462GSZ
OP37EP	OP4177AR	OP421GY	OP462HRU-REEL
OP37EZ	OP4177ARU	OP421HP	OP462HRUZ-REEL
OP37FJ	OP4177ARUZ	OP421HS	OP467ARC/883
OP37FP	OP4177ARZ	OP421HY	OP467AY/883
OP37FZ	OP41AJ	OP42AJ	OP467GP

Multisim 14.0 Base Components

OP467GS	OP491GSZ	OP50EY	OP77GP
OP470ARC/883	OP492GP	OP50FY	OP77GS
OP470ATC/883	OP492GS	OP61ARC/883	OP80BJ
OP470AY	OP493EP	OP61AZ	OP80EJ
OP470EY	OP493ES	OP61FZ	OP80FJ
OP470GP	OP493FP	OP61GP	OP80GP
OP470GS	OP493FS	OP61GS	OP80GS
OP481GRU	OP495GP	OP64AJ	OP906
OP481GS	OP495GS	OP64ARC/883	OP90ARC/883
OP482ARC/883	OP495GSZ	OP64AZ	OP90AZ
OP482AY/883	OP496GP	OP64GP	OP90EZ
OP482GP	OP496GS	OP64GS	OP90FZ
OP484EP	OP496HRU	OP727AR	OP90GP
OP484ES	OP497AY	OP727ARU	OP90GS
OP484FP	OP497BRC/883	OP727ARUZ	OP950
OP484FPZ	OP497BY	OP747AR	OP97AJ
OP484FS	OP497CY	OP747ARU	OP97AZ
OP490ATC/883	OP497FP	OP777AR	OP97EP
OP490AY	OP497FS	OP777ARM	OP97FJ
OP490EY	OP497FY	OP77BJ	OP97FP
OP490FY	OP497GP	OP77BRC/883	OP97FS
OP490GP	OP497GS	OP77BZ	OP97FZ
OP490GS	OP497GY	OP77EZ	OP999
OP491GP	OP50AY	OP77FJ	OPA1013CN8
OP491GS	OP50BY	OP77FZ	OPA1013DN8

Multisim 14.0 Base Components

OPA111AM	OPA137NA	OPA209AID	OPA2131UJ
OPA111BM	OPA137P	OPA209AIDBVR	OPA2134PA
OPA111SM	OPA137PA	OPA209AIDGKR	OPA2134UA
OPA121KM	OPA137U	OPA209AIDR	OPA2140AID
OPA121KP	OPA137UA	OPA2107AM	OPA2140AIDGKR
OPA121KU	OPA140AID	OPA2107AP	OPA2140AIDR
OPA124P	OPA140AIDBVR	OPA2107AU	OPA2141AIDGKR
OPA124PA	OPA140AIDGKR	OPA2107BM	OPA2141AIDR
OPA124PB	OPA140AIDR	OPA2107SM	OPA2209AID
OPA124U	OPA141AIDGKR	OPA2111AM	OPA2209AIDGKR
OPA124UA	OPA141AIDR	OPA2111BM	OPA2209AIDR
OPA124UB	OPA1612AID	OPA2111KM	OPA228P
OPA128JM	OPA1632D	OPA2111KP	OPA228U
OPA128KM	OPA1632DGN	OPA2111SM	OPA2300AIDGSR
OPA128LM	OPA1642AID	OPA211AID	OPA2301AID
OPA128SM	OPA1642AIDGKR	OPA211AIDGKR	OPA2301AIDGKR
OPA129P	OPA1642AIDR	OPA211AIDR	OPA2301AIDR
OPA129PB	OPA1644AID	OPA211AIDRGR	OPA2317ID
OPA129U	OPA1644AIPW	OPA211ID	OPA2317IDGKR
OPA129UB	OPA177EZ	OPA211IDGKR	OPA2330AID
OPA131PA	OPA177FP	OPA211IDR	OPA2330AIDGKR
OPA131PJ	OPA177FZ	OPA211IDRGR	OPA2330AIDR
OPA131UA	OPA177GP	OPA2131PA	OPA2330AIDRBR
OPA131UJ	OPA177GS	OPA2131PJ	OPA2330AIDRG4
OPA137N	OPA177GZ	OPA2131UA	OPA2333AIDGKR

Multisim 14.0 Base Components

OPA2333AIDR	OPA2354AIDGKR	OPA2381AIDGKR	OPA2684IDCNR
OPA2333AIDRBR	OPA2355DGSA/250	OPA2381AIDRBT	OPA2690I-14D
OPA2333AIDRG4	OPA2357AIDGSR	OPA2541AM	OPA2690ID
OPA2334AIDGSR	OPA2363AIDGSR	OPA2541BM	OPA2691I-14D
OPA2335AID	OPA2363AIRSVR	OPA2541SM	OPA2691ID
OPA2335AIDGKR	OPA2363IDGSR	OPA2544T	OPA2703EA/250
OPA2335AIDR	OPA2369AIDCNR	OPA2604AP	OPA2703PA
OPA2337EA/250	OPA2369AIDGKR	OPA2604AU	OPA2703UA
OPA2337PA	OPA2373AIDGSR	OPA2613ID	OPA2704EA/250
OPA2337UA	OPA2373AIDRCR	OPA2613IDTJ	OPA2704PA
OPA2338EA/250	OPA2374AID	OPA2614ID	OPA2704UA
OPA2338UA	OPA2374AIDCNR	OPA2614IDTJ	OPA2725AID
OPA2344EA/250	OPA2374AIDG4	OPA2652E	OPA2725AIDGKR
OPA2344PA	OPA2376AID	OPA2652U	OPA2725AIDR
OPA2344UA	OPA2376AIDGKR	OPA2658P	OPA2726AIDGST
OPA2347EA	OPA2376AIDR	OPA2658PB	OPA2727AID
OPA2347UA	OPA2376AIYZDR	OPA2658U	OPA2727AIDRBR
OPA2349EA/250	OPA2377AID	OPA2658UB	OPA2727AIDRG4
OPA2349UA	OPA2377AIDGKR	OPA2677T	OPA2735AID
OPA2350EA	OPA2377AIDR	OPA2677U	OPA2735AIDGKR
OPA2350PA	OPA2378AIDCNR	OPA2683ID	OPA2735AIDR
OPA2350UA	OPA2379AID	OPA2683IDCNR	OPA2743EA/250
OPA2353EA/250	OPA2379AIDCNR	OPA2683IDG4	OPA2743PA
OPA2353UA	OPA2379AIDG4	OPA2683IDGST	OPA2743UA
OPA2354AIDDA	OPA2380AIDGKR	OPA2684ID	OPA27AJ

Multisim 14.0 Base Components

OPA27AZ	OPA301AID	OPA338NA/250	OPA354AIDDA
OPA27BJ	OPA301AIDBV	OPA338UA	OPA355NA
OPA27BZ	OPA317ID	OPA343NA	OPA355UA
OPA27CJ	OPA317IDBVR	OPA343UA	OPA357AIDBV
OPA27CZ	OPA317IDCKR	OPA344NA	OPA3583AM
OPA27EJ	OPA320AIDBVR	OPA344PA	OPA3583JM
OPA27EZ	OPA320SAIDBVR	OPA344UA	OPA358AIDCK
OPA27FJ	OPA333AID	OPA345NA	OPA360AIDCK
OPA27FZ	OPA333AIDBVR	OPA345UA	OPA363ID
OPA27GJ	OPA333AIDCKR	OPA347NA	OPA363IDBV
OPA27GP	OPA333AIDG4	OPA347PA	OPA364ID
OPA27GU	OPA334AID	OPA347SA	OPA364IDBV
OPA27GZ	OPA335EA/250	OPA347UA	OPA365AID
OPA2822E/250	OPA335UA	OPA348AID	OPA365AIDBVR
OPA2822U	OPA335AID	OPA348AIDBV	OPA3690ID
OPA2835ID	OPA335AIDBV	OPA348AIDCKR	OPA3690IDBQR
OPA2835IDGS	OPA336N/250	OPA349NA	OPA3690IDG4
OPA2835IRMCR	OPA336NA/250	OPA349SA	OPA369AIDCKR
OPA2835IRUNR	OPA336NJ/250	OPA349UA	OPA373AID
OPA2836ID	OPA336U	OPA350EA	OPA373AIDBV
OPA2836IDGS	OPA336UA	OPA350PA	OPA374AID
OPA2836IRUNR	OPA337EA/250	OPA350UA	OPA374AIDBV
OPA2846ID	OPA337NA/250	OPA353NA	OPA377AID
OPA300AID	OPA337PA	OPA353UA	OPA377AIDBVR
OPA300AIDBV	OPA337UA	OPA354AIDBV	OPA377AIDCKR

Multisim 14.0 Base Components

OPA377AIDR	OPA404BG	OPA4243EA	OPA445BM
OPA378AIDBVR	OPA404KP	OPA4244EA	OPA445SM
OPA378AIDCKR	OPA404KU	OPA4251PA	OPA452TA
OPA379AID	OPA404SG	OPA4251UA	OPA454AIDDA
OPA379AIDBVR	OPA4131NA	OPA4277PA	OPA4650P
OPA379AIDCKR	OPA4131NJ	OPA4277UA	OPA4650PB
OPA379AIDG4	OPA4131PA	OPA4317ID	OPA4650U
OPA37AJ	OPA4131PJ	OPA4317IPW	OPA4658P
OPA37AZ	OPA4131UA	OPA4330AID	OPA4658PB
OPA37BJ	OPA4134UA	OPA4330AIPW	OPA4658U
OPA37BZ	OPA4137P	OPA4330AIRGYR	OPA4658UB
OPA37CJ	OPA4137PA	OPA4342EA	OPA4684ID
OPA37CZ	OPA4137U	OPA4342PA	OPA4684IPWT
OPA37EJ	OPA4137UA	OPA4342UA	OPA4703EA/250
OPA37EZ	OPA4140AID	OPA4347EA	OPA4703UA
OPA37FJ	OPA4140AIPW	OPA4347UA	OPA4704EA/250
OPA37FZ	OPA4141AID	OPA4348AID	OPA4704UA
OPA37GJ	OPA4141AIPW	OPA4348AIP	OPA4743EA/250
OPA37GP	OPA4209AIPW	OPA4354AID	OPA4743UA
OPA37GU	OPA4227PA	OPA4354AIPWR	OPA4820ID
OPA37GZ	OPA4227UA	OPA4374AID	OPA4820IPWR
OPA380AID	OPA4228PA	OPA4374AIPWR	OPA501AM
OPA380AIDGK	OPA4228UA	OPA4377AIPW	OPA501BM
OPA381AIDGK	OPA4241PA	OPA4379AIPWR	OPA501RM
OPA404AG	OPA4241UA	OPA445AP	OPA501SM

Multisim 14.0 Base Components

OPA502BM	OPA564AIDWP	OPA620SG	OPA640H
OPA502SM	OPA567AIRHGR	OPA621KG	OPA640HSQ
OPA511AM	OPA569AIDWP	OPA621KP	OPA640P
OPA512BM	OPA600BM	OPA621KU	OPA640U
OPA512SM	OPA600CM	OPA621LG	OPA640UB
OPA541AM	OPA600SM	OPA621SG	OPA641H
OPA541AP	OPA600TM	OPA622AP	OPA641HSQ
OPA541BM	OPA602AM	OPA622AU	OPA641P
OPA541SM	OPA602AP	OPA623AP	OPA641PB
OPA544F	OPA602AU	OPA623AU	OPA641U
OPA544T	OPA602BM	OPA627AM	OPA641UB
OPA547T	OPA602BP	OPA627AP	OPA642H
OPA548T	OPA602CM	OPA627AU	OPA642HSQ
OPA549S	OPA602SM	OPA627BM	OPA642P
OPA549T	OPA603AP	OPA627BP	OPA642PB
OPA551FA/500	OPA603AU	OPA627SM	OPA642U
OPA551FAKTWT	OPA604AP	OPA628AP	OPA642UB
OPA551PA	OPA604AU	OPA628AU	OPA643H
OPA551UA	OPA606KM	OPA633KP	OPA643HSQ
OPA552FA/500	OPA606KP	OPA637AM	OPA643P
OPA552FAKTWT	OPA606LM	OPA637AP	OPA643PB
OPA552PA	OPA620KG	OPA637AU	OPA643U
OPA552UA	OPA620KP	OPA637BM	OPA643UB
OPA561PWP	OPA620KU	OPA637BP	OPA644U
OPA564AIDWD	OPA620LG	OPA637SM	OPA644UB

Multisim 14.0 Base Components

OPA646H	OPA655HSQ	OPA681N	OPA704UA
OPA646HSQ	OPA655P	OPA681P	OPA725AID
OPA646P	OPA655PB	OPA681U	OPA725AIDBV
OPA646PB	OPA655UB	OPA682N	OPA726AID
OPA646U	OPA656N	OPA682P	OPA726AIDGK
OPA646UB	OPA656U	OPA682U	OPA727AIDGKR
OPA648H	OPA658N	OPA683BV	OPA727AIDRBT
OPA648P	OPA658P	OPA683ID	OPA728AIDGKT
OPA648U	OPA658U	OPA684ID	OPA728AIDRBT
OPA650N	OPA659IDBVR	OPA684IDBV	OPA734AID
OPA650NB	OPA659IDRBR	OPA686N	OPA734AIDBV
OPA650P	OPA671AP	OPA686U	OPA735AID
OPA650PB	OPA675JG	OPA687N	OPA735AIDBV
OPA650U	OPA675KG	OPA687U	OPA743NA
OPA650UB	OPA675SG	OPA690ID	OPA743PA
OPA651N	OPA676JG	OPA690IDBV	OPA743UA
OPA651NB	OPA676KG	OPA694ID	OPA77EZ
OPA651P	OPA676SG	OPA694IDBVR	OPA77FP
OPA651PB	OPA678AG	OPA698ID	OPA77FZ
OPA651U	OPA678AP	OPA699ID	OPA77GP
OPA651UB	OPA678AU	OPA703NA	OPA820ID
OPA653IDBVR	OPA678SG	OPA703PA	OPA820IDBVR
OPA653IDRBR	OPA680N	OPA703UA	OPA820IDG4
OPA654AM	OPA680P	OPA704NA	OPA827AID
OPA655H	OPA680U	OPA704PA	OPA827AIDGKR

Multisim 14.0 Base Components

OPA835IDBVR	OR8	P6SMB24CA-E3/52	PBHV9040Z
OPA836IDBVR	OSTV7163151	P6SMB24CAT3G	PBHV9050T
OPA842ID	OSTV7203101	P6SMB33A-E3/52	PBHV9050Z
OPA842IDBV	OSTV7203151	P6SMB33AT3G	PBHV9115T
OPA847ID	OVERLOAD	P6SMB36A-E3/52	PBHV9115X
OPA847IDBV	P4KE10CA-E3/54	P6SMB43CAT3G	PBHV9115Z
OPAMP_3T_VIRTU AL	P4KE300A/3	P6SMB6.8AT3G	PBHV9215Z
	P4SMA36CA-E3/61	P6SMB62AT3G	PBHV9540Z
OPAMP_5T_VIRTU AL	P6KE100A-E3/54	P6SMB68AT3G	PBLS1501V
	P6KE10A-E3/54	PAR_GEN_CHK	PBLS1501Y
OPT301M	P6KE200AG	PB_DPST	PBLS1502V
	P6KE200ARLG	PB_DPST	PBLS1502Y
OR2	P6KE6.8AG	PB_NC	PBLS1503V
	P6KE6.8ARLG	PB_NO	PBLS1503Y
OR3	P6KE8.2A-E3/54	PBHV8115T	PBLS1504V
OR3	P6KE9.1A-E3/54	PBHV8115X	PBLS1504Y
OR4	P6SMB11CAT3G	PBHV8115Z	PBLS2001D
OR4	P6SMB13AT3G	PBHV8118T	PBLS2001S
OR5	P6SMB15AT3G	PBHV8140Z	PBLS2002D
OR5	P6SMB18AT3G	PBHV8215Z	PBLS2002S
OR6	P6SMB20AT3G	PBHV8540T	PBLS2003D
OR6	P6SMB22AT3G	PBHV8540X	PBLS2003S
OR7	P6SMB22CAT3G	PBHV8540Z	PBLS2004D
OR7	P6SMB24A-E3/52	PBHV9040T	PBLS2021D
OR8	P6SMB24AT3G	PBHV9040X	PBLS2022D

Multisim 14.0 Base Components

PBLS2023D	PBLS6024D	PBSS302NX	PBSS306PX
PBLS2024D	PBRN113ET	PBSS302NZ	PBSS306PZ
PBLS4001D	PBRN113ZT	PBSS302PD	PBSS3515E
PBLS4001V	PBRN123ET	PBSS302PX	PBSS3515M
PBLS4001Y	PBRN123YT	PBSS302PZ	PBSS3515MB
PBLS4002D	PBRP113ET	PBSS303ND	PBSS3515VS
PBLS4002V	PBRP113ZT	PBSS303NX	PBSS3540E
PBLS4002Y	PBRP123ET	PBSS303NZ	PBSS3540M
PBLS4003D	PBRP123YT	PBSS303PD	PBSS3540MB
PBLS4003V	PBSS2515E	PBSS303PX	PBSS4021NT
PBLS4003Y	PBSS2515M	PBSS303PZ	PBSS4021NX
PBLS4004D	PBSS2515MB	PBSS304ND	PBSS4021NZ
PBLS4004V	PBSS2515VPN	PBSS304NX	PBSS4021PT
PBLS4004Y	PBSS2515VS	PBSS304NZ	PBSS4021PX
PBLS4005D	PBSS2515YPN	PBSS304PD	PBSS4021PZ
PBLS4005V	PBSS2540E	PBSS304PX	PBSS4021SN
PBLS4005Y	PBSS2540M	PBSS304PZ	PBSS4021SP
PBLS6001D	PBSS2540MB	PBSS305ND	PBSS4021SPN
PBLS6002D	PBSS301ND	PBSS305NX	PBSS4032ND
PBLS6003D	PBSS301NX	PBSS305NZ	PBSS4032NT
PBLS6004D	PBSS301NZ	PBSS305PD	PBSS4032NX
PBLS6005D	PBSS301PD	PBSS305PX	PBSS4032NZ
PBLS6021D	PBSS301PX	PBSS305PZ	PBSS4032PD
PBLS6022D	PBSS301PZ	PBSS306NX	PBSS4032PT
PBLS6023D	PBSS302ND	PBSS306NZ	PBSS4032PX

Multisim 14.0 Base Components

PBSS4032PZ	PBSS4160DS	PBSS4350D	PBSS5140V
PBSS4032SN	PBSS4160PAN	PBSS4350SPN	PBSS5160DS
PBSS4032SP	PBSS4160PANP	PBSS4350SS	PBSS5160PAP
PBSS4032SPN	PBSS4160QA	PBSS4350T	PBSS5160QA
PBSS4041NT	PBSS4160T	PBSS4350X	PBSS5160T
PBSS4041NX	PBSS4160U	PBSS4350Z	PBSS5160U
PBSS4041NZ	PBSS4160V	PBSS4360Z	PBSS5160V
PBSS4041PT	PBSS4220V	PBSS4420D	PBSS5220T
PBSS4041PX	PBSS4230PAN	PBSS4440D	PBSS5220V
PBSS4041PZ	PBSS4230PANP	PBSS4480X	PBSS5230PAP
PBSS4041SN	PBSS4230QA	PBSS4520X	PBSS5230QA
PBSS4041SP	PBSS4230T	PBSS4540X	PBSS5230T
PBSS4041SPN	PBSS4240DPN	PBSS4540Z	PBSS5240T
PBSS4112PAN	PBSS4240T	PBSS4560PA	PBSS5240V
PBSS4112PANP	PBSS4240V	PBSS4580PA	PBSS5240X
PBSS4120T	PBSS4240X	PBSS4612PA	PBSS5240Y
PBSS4130PAN	PBSS4240Y	PBSS4620PA	PBSS5250T
PBSS4130PANP	PBSS4250X	PBSS4630PA	PBSS5250X
PBSS4130QA	PBSS4260PAN	PBSS5112PAP	PBSS5260PAP
PBSS4130T	PBSS4260PANP	PBSS5120T	PBSS5260QA
PBSS4140DPN	PBSS4260QA	PBSS5130PAP	PBSS5320D
PBSS4140T	PBSS4320T	PBSS5130QA	PBSS5320T
PBSS4140U	PBSS4320X	PBSS5130T	PBSS5320X
PBSS4140V	PBSS4330PA	PBSS5140T	PBSS5330PA
PBSS4160DPN	PBSS4330X	PBSS5140U	PBSS5330X

Multisim 14.0 Base Components

PBSS5350D	PBSS9110X	PDTA113ZU	PDTA115TU
PBSS5350SS	PBSS9110Y	PDTA114EE	PDTA123EE
PBSS5350T	PBSS9110Z	PDTA114EM	PDTA123EM
PBSS5350X	PBSS9410PA	PDTA114EMB	PDTA123EMB
PBSS5350Z	PCP1208-TD-H	PDTA114ET	PDTA123ET
PBSS5360Z	PD15-22B/TR8	PDTA114EU	PDTA123EU
PBSS5420D	PD15-22C/TR8	PDTA114TE	PDTA123JE
PBSS5440D	PD70-01B/TR7	PDTA114TM	PDTA123JM
PBSS5480X	PD93-21C/TR8	PDTA114TMB	PDTA123JMB
PBSS5520X	PD95-21B/TR10	PDTA114TT	PDTA123JT
PBSS5540X	PDB-C134	PDTA114TU	PDTA123JU
PBSS5540Z	PDB-C134F	PDTA114YE	PDTA123TM
PBSS5560PA	PDB-C139	PDTA114YM	PDTA123TMB
PBSS5580PA	PDB-C142D	PDTA114YMB	PDTA123TT
PBSS5612PA	PDB-C152SM	PDTA114YT	PDTA123TU
PBSS5620PA	PDB-C156	PDTA114YU	PDTA123YE
PBSS5630PA	PDTA113EE	PDTA115EE	PDTA123YM
PBSS8110D	PDTA113EM	PDTA115EM	PDTA123YMB
PBSS8110T	PDTA113EMB	PDTA115EMB	PDTA123YT
PBSS8110X	PDTA113ET	PDTA115ET	PDTA123YU
PBSS8110Y	PDTA113EU	PDTA115EU	PDTA124EE
PBSS8110Z	PDTA113ZE	PDTA115TE	PDTA124EM
PBSS8510PA	PDTA113ZM	PDTA115TM	PDTA124EMB
PBSS9110D	PDTA113ZMB	PDTA115TMB	PDTA124ET
PBSS9110T	PDTA113ZT	PDTA115TT	PDTA124EU

Multisim 14.0 Base Components

PDTA124TE	PDTA143ZE	PDTB113ET	PDTC115TE
PDTA124TM	PDTA143ZM	PDTB113ZT	PDTC115TM
PDTA124TMB	PDTA143ZMB	PDTB123ET	PDTC115TMB
PDTA124TT	PDTA143ZT	PDTB123TT	PDTC115TT
PDTA124TU	PDTA143ZU	PDTB123YT	PDTC115TU
PDTA124XE	PDTA144EE	PDTC114EE	PDTC123EE
PDTA124XM	PDTA144EM	PDTC114EM	PDTC123EM
PDTA124XMB	PDTA144EMB	PDTC114EMB	PDTC123EMB
PDTA124XT	PDTA144ET	PDTC114ET	PDTC123ET
PDTA124XU	PDTA144EU	PDTC114EU	PDTC123EU
PDTA143EE	PDTA144TE	PDTC114TE	PDTC123JE
PDTA143EM	PDTA144TM	PDTC114TM	PDTC123JM
PDTA143EMB	PDTA144TMB	PDTC114TMB	PDTC123JMB
PDTA143ET	PDTA144TT	PDTC114TT	PDTC123JT
PDTA143EU	PDTA144TU	PDTC114TU	PDTC123JU
PDTA143TE	PDTA144VE	PDTC114YE	PDTC123TE
PDTA143TM	PDTA144VM	PDTC114YM	PDTC123TM
PDTA143TMB	PDTA144VMB	PDTC114YMB	PDTC123TMB
PDTA143TT	PDTA144VT	PDTC114YT	PDTC123TT
PDTA143TU	PDTA144VU	PDTC114YU	PDTC123TU
PDTA143XE	PDTA144WE	PDTC115EE	PDTC123YE
PDTA143XM	PDTA144WM	PDTC115EM	PDTC123YM
PDTA143XMB	PDTA144WMB	PDTC115EMB	PDTC123YMB
PDTA143XT	PDTA144WT	PDTC115ET	PDTC123YT
PDTA143XU	PDTA144WU	PDTC115EU	PDTC123YU

Multisim 14.0 Base Components

PDTC124EE	PDTC143XE	PDTC144WE	PDZ4.3B
PDTC124EM	PDTC143XM	PDTC144WM	PDZ4.7B
PDTC124EMB	PDTC143XMB	PDTC144WMB	PDZ5.1B
PDTC124ET	PDTC143XT	PDTC144WT	PDZ5.6B
PDTC124EU	PDTC143XU	PDTC144WU	PDZ6.2B
PDTC124TE	PDTC143ZE	PDTD113ET	PDZ6.8B
PDTC124TM	PDTC143ZM	PDTD113ZT	PDZ7.5B
PDTC124TMB	PDTC143ZMB	PDTD123ET	PDZ9.1B
PDTC124TT	PDTC143ZT	PDTD123TT	PEMB1
PDTC124TU	PDTC143ZU	PDTD123YT	PEMB10
PDTC124XE	PDTC144EE	PDZ10B	PEMB11
PDTC124XM	PDTC144EM	PDZ11B	PEMB13
PDTC124XMB	PDTC144EMB	PDZ12B	PEMB14
PDTC124XT	PDTC144ET	PDZ13B	PEMB15
PDTC124XU	PDTC144EU	PDZ15B	PEMB16
PDTC143EE	PDTC144TE	PDZ16B	PEMB17
PDTC143EM	PDTC144TM	PDZ18B	PEMB18
PDTC143EMB	PDTC144TMB	PDZ2.7B	PEMB19
PDTC143ET	PDTC144TT	PDZ20B	PEMB2
PDTC143EU	PDTC144TU	PDZ22B	PEMB20
PDTC143TE	PDTC144VE	PDZ24B	PEMB24
PDTC143TM	PDTC144VM	PDZ3.0B	PEMB3
PDTC143TMB	PDTC144VMB	PDZ3.3B	PEMB30
PDTC143TT	PDTC144VT	PDZ3.6B	PEMB4
PDTC143TU	PDTC144VU	PDZ3.9B	PEMB9

Multisim 14.0 Base Components

PEMD10	PEMH16	PESD12VS4UD	PESD24VS2UAT
PEMD12	PEMH17	PESD12VS5UD	PESD24VS2UQ
PEMD13	PEMH18	PESD12VU1UT	PESD24VS2UT
PEMD14	PEMH19	PESD12VV1BL	PESD24VS4UD
PEMD15	PEMH2	PESD15VL1BA	PESD24VS5UD
PEMD16	PEMH20	PESD15VL2BT	PESD24VU1UT
PEMD17	PEMH24	PESD15VS1UB	PESD2CAN
PEMD18	PEMH30	PESD15VS1UL	PESD36VS1UL
PEMD19	PEMH4	PESD15VS1ULD	PESD36VS2UT
PEMD2	PEMH7	PESD15VS2UAT	PESD3V3L1BA
PEMD20	PEMH9	PESD15VS2UQ	PESD3V3L1UA
PEMD24	PEMT1	PESD15VS2UT	PESD3V3L1UB
PEMD3	PEMX1	PESD15VS4UD	PESD3V3L1UL
PEMD30	PEMZ1	PESD15VS5UD	PESD3V3L2BT
PEMD4	PEMZ7	PESD15VU1UT	PESD3V3L2UM
PEMD48	PESD12VL1BA	PESD16VX1UL	PESD3V3L4UF
PEMD6	PESD12VL2BT	PESD1CAN	PESD3V3L4UG
PEMD9	PESD12VS1UA	PESD1FLEX	PESD3V3L4UW
PEMF21	PESD12VS1UB	PESD1LIN	PESD3V3L5UF
PEMH1	PESD12VS1UJ	PESD24VL1BA	PESD3V3L5UK
PEMH10	PESD12VS1UL	PESD24VL2BT	PESD3V3L5UV
PEMH11	PESD12VS1ULD	PESD24VS1UA	PESD3V3L5UY
PEMH13	PESD12VS2UAT	PESD24VS1UB	PESD3V3S1UB
PEMH14	PESD12VS2UQ	PESD24VS1UL	PESD3V3S1UL
PEMH15	PESD12VS2UT	PESD24VS1ULD	PESD3V3S2UAT

Multisim 14.0 Base Components

PESD3V3S2UQ	PESD5V0L5UV	PESD5V0U1UA	PESD9X7.0L
PESD3V3S2UT	PESD5V0L5UY	PESD5V0U1UB	PG_13
PESD3V3S4UD	PESD5V0L6UAS	PESD5V0U1UL	PG_9_O_E
PESD3V3S4UF	PESD5V0L6US	PESD5V0U1UT	PHILIPS-MIPS-HDR
PESD3V3S5UD	PESD5V0L7BAS	PESD5V0U2BT	PHN110
PESD3V3U1UT	PESD5V0L7BS	PESD5V0V1BA	PhonePlug
PESD3V3V4UF	PESD5V0S1BA	PESD5V0V1BB	PhonePlug2
PESD3V3V4UG	PESD5V0S1BB	PESD5V0V1BL	PHOTODIODE
PESD3V3V4UK	PESD5V0S1BL	PESD5V0V1BLD	PHOTOTRANSISTOR
PESD3V3V4UW	PESD5V0S1BLD	PESD5V0V4UF	PHP125
PESD5V0F1BL	PESD5V0S1UA	PESD5V0V4UG	PHP225
PESD5V0F1BLD	PESD5V0S1UB	PESD5V0V4UK	PHPT60603NY
PESD5V0F5UF	PESD5V0S1UJ	PESD5V0V4UW	PHPT60603PY
PESD5V0F5UV	PESD5V0S1UL	PESD5V0X1BCAL	PHPT61002NYC
PESD5V0L1BA	PESD5V0S1ULD	PESD5V0X1BCL	PHPT61002PYC
PESD5V0L1UA	PESD5V0S2BT	PESD5V0X1BL	PHPT61003NY
PESD5V0L1UB	PESD5V0S2UAT	PESD5V0X1BQ	PHPT61003PY
PESD5V0L1UL	PESD5V0S2UQ	PESD5V0X1BT	PHT4NQ10LT
PESD5V0L1ULD	PESD5V0S4UD	PESD5V0X1UAB	PHT6N06LT
PESD5V0L2BT	PESD5V0S4UF	PESD5V0X1UALD	PHT6N06T
PESD5V0L2UM	PESD5V0S5UD	PESD5V0X1UB	PHT6NQ10T
PESD5V0L4UF	PESD5V0U1BA	PESD5V0X1ULD	PHT8N06LT
PESD5V0L4UG	PESD5V0U1BB	PESD5V2S2UT	PIC12C508
PESD5V0L4UW	PESD5V0U1BL	PESD9V0V4UK	PIC12C508A
PESD5V0L5UK	PESD5V0U1BLD	PESD9X5.0L	PIC12C509

Multisim 14.0 Base Components

PIC12C509A	PIC18F8720- TQFP(80L)	PMBD353	PMBFJ177
PIC12CE518		PMBD354	PMBFJ210
PIC12CE519	PIECEWISE_LINEAR _CURRENT	PMBD6050	PMBFJ211
PIC12CR509A	PIECEWISE_LINEAR _VOLTAGE	PMBD6100	PMBFJ212
PIC16C505		PMBD7000	PMBFJ308
PIC16C54	PIMC31	PMBD7100	PMBFJ309
PIC16C54A	PIMN31	PMBD914	PMBFJ310
PIC16C54C	PIMT1	PMBF170	PMBS3904
PIC16C554	PIMZ2	PMBF4391	PMBS3906
PIC16C558	PJ-002B-SMT	PMBF4392	PMBT2222
PIC16C56	PJ-007	PMBF4393	PMBT2222A
PIC16C56A	PJ1-023	PMBF4416	PMBT2369
PIC16C58B	PJ-102A	PMBF4416A	PMBT2907
PIC16CR54A	PLD-JTAG-HDR	PMBF5484	PMBT2907A
PIC16CR54C	PLL_VIRTUAL	PMBF5485	PMBT3904
PIC16CR56A	PLUS_MINUS_ONE	PMBF5486	PMBT3904M
PIC16CR58B	PLUS_MINUS_ONE_ BLUE	PMBFJ108	PMBT3904MB
PIC16CR83	PLUS_MINUS_ONE_ GREEN	PMBFJ109	PMBT3904VS
PIC16CR84		PMBFJ110	PMBT3904YS
PIC16F83	PLUS_MINUS_ONE_ ORANGE	PMBFJ111	PMBT3906
PIC18F6620- TQFP(64L)	PLUS_MINUS_ONE_ YELLOW	PMBFJ112	PMBT3906M
PIC18F6720- TQFP(64L)		PMBFJ113	PMBT3906MB
PIC18F8620- TQFP(80L)	PLVA2656A	PMBFJ174	PMBT3906VS
	PLVA650A	PMBFJ175	PMBT3906YS
	PLVA662A	PMBFJ176	PMBT3946VPN

Multisim 14.0 Base Components

PMBT3946YPN	PMBZ5234B	PMDPB30XN	PMEG2005CT
PMBT4401	PMBZ5235B	PMDPB38UNE	PMEG2005EB
PMBT4403	PMBZ5236B	PMDPB42UN	PMEG2005EH
PMBT5550	PMBZ5237B	PMDPB55XP	PMEG2005EJ
PMBT5551	PMBZ5238B	PMDPB56XN	PMEG2005EL
PMBT6428	PMBZ5239B	PMDPB58UPE	PMEG2005ELD
PMBT6429	PMBZ5240B	PMDPB70EN	PMEG2005EPK
PMBTA06	PMBZ5241B	PMDPB70XP	PMEG2005ESF
PMBTA13	PMBZ5242B	PMDPB70XPE	PMEG2005ET
PMBTA14	PMBZ5243B	PMDPB85UPE	PMEG2010AEB
PMBTA42	PMBZ5244B	PMDPB95XNE	PMEG2010AEH
PMBTA42DS	PMBZ5245B	PMDT290UNE	PMEG2010AEJ
PMBTA44	PMBZ5246B	PMDT670UPE	PMEG2010AET
PMBTA45	PMBZ5247B	PMEG1020EA	PMEG2010BEA
PMBTA56	PMBZ5248B	PMEG1020EH	PMEG2010BELD
PMBTA64	PMBZ5249B	PMEG1020EJ	PMEG2010BER
PMBTA92	PMBZ5250B	PMEG1020EV	PMEG2010BEV
PMBZ5226B	PMBZ5251B	PMEG1030EH	PMEG2010EA
PMBZ5227B	PMBZ5252B	PMEG1030EJ	PMEG2010EH
PMBZ5228B	PMBZ5253B	PMEG2005AEA	PMEG2010EJ
PMBZ5229B	PMBZ5254B	PMEG2005AEL	PMEG2010EPA
PMBZ5230B	PMBZ5255B	PMEG2005AELD	PMEG2010EPK
PMBZ5231B	PMBZ5256B	PMEG2005AESF	PMEG2010ER
PMBZ5232B	PMBZ5257B	PMEG2005AEV	PMEG2010ET
PMBZ5233B	PMDPB28UN	PMEG2005BELD	PMEG2010EV

Multisim 14.0 Base Components

PMEG2015EA	PMEG3005ELD	PMEG3020EP	PMEG4010EH
PMEG2015EH	PMEG3005ESF	PMEG3020EPA	PMEG4010EJ
PMEG2015EJ	PMEG3005ET	PMEG3020ER	PMEG4010EP
PMEG2015EPK	PMEG3010BEA	PMEG3030BEP	PMEG4010EPK
PMEG2015EV	PMEG3010BEP	PMEG3030EP	PMEG4010ER
PMEG2020AEA	PMEG3010BER	PMEG3050BEP	PMEG4010ET
PMEG2020CPA	PMEG3010BEV	PMEG3050EP	PMEG4010ETP
PMEG2020EH	PMEG3010CEH	PMEG4002AESF	PMEG4010ETR
PMEG2020EJ	PMEG3010CEJ	PMEG4002EB	PMEG4015EPK
PMEG2020EPA	PMEG3010EB	PMEG4002EJ	PMEG4020EP
PMEG2020EPK	PMEG3010EH	PMEG4002EL	PMEG4020EPA
PMEG3002AEB	PMEG3010EJ	PMEG4002ELD	PMEG4020EPK
PMEG3002AEL	PMEG3010EP	PMEG4002ESF	PMEG4020ER
PMEG3002AELD	PMEG3010ER	PMEG4005AEA	PMEG4020ETP
PMEG3002AESF	PMEG3010ET	PMEG4005AEV	PMEG4020ETR
PMEG3002EJ	PMEG3015EH	PMEG4005CT	PMEG4030EP
PMEG3002TV	PMEG3015EJ	PMEG4005EH	PMEG4030ER
PMEG3005AEA	PMEG3015EV	PMEG4005EJ	PMEG4030ETP
PMEG3005AESF	PMEG3020BEP	PMEG4005EPK	PMEG4050EP
PMEG3005AEV	PMEG3020BER	PMEG4005ET	PMEG4050ETP
PMEG3005CT	PMEG3020CEP	PMEG4010BEA	PMEG45A10EPD
PMEG3005EB	PMEG3020CPA	PMEG4010BEV	PMEG45U10EPD
PMEG3005EH	PMEG3020DEP	PMEG4010CEH	PMEG6002EB
PMEG3005EJ	PMEG3020EH	PMEG4010CEJ	PMEG6002EJ
PMEG3005EL	PMEG3020EJ	PMEG4010CPA	PMEG6002TV

Multisim 14.0 Base Components

PMEG6010AED	PMF87EN	PMLL5237B	PMLL5262B
PMEG6010CEH	PMG45UN	PMLL5238B	PMLL5263B
PMEG6010CEJ	PMG85XP	PMLL5239B	PMLL5264B
PMEG6010CPA	PMGD130UN	PMLL5240B	PMLL5265B
PMEG6010ELR	PMGD175XN	PMLL5241B	PMLL5266B
PMEG6010EP	PMGD280UN	PMLL5242B	PMMT491A
PMEG6010ER	PMGD290XN	PMLL5243B	PMMT591A
PMEG6010ETR	PMGD370XN	PMLL5244B	PMN20EN
PMEG6020ELR	PMGD400UN	PMLL5245B	PMN22XN
PMEG6020EP	PMGD780SN	PMLL5246B	PMN25EN
PMEG6020EPA	PMGD8000LN	PMLL5247B	PMN25UN
PMEG6020ER	PMLL4148L	PMLL5248B	PMN27UP
PMEG6020ETP	PMLL4448	PMLL5249B	PMN27XPE
PMEG6020ETR	PMLL5225B	PMLL5250B	PMN28UN
PMEG6030EP	PMLL5226B	PMLL5251B	PMN34UN
PMEG6030ETP	PMLL5227B	PMLL5252B	PMN34UP
PMF170XP	PMLL5228B	PMLL5253B	PMN35EN
PMF250XN	PMLL5229B	PMLL5254B	PMN40LN
PMF280UN	PMLL5230B	PMLL5255B	PMN40UPE
PMF290XN	PMLL5231B	PMLL5256B	PMN42XPE
PMF3800SN	PMLL5232B	PMLL5257B	PMN48XP
PMF400UN	PMLL5233B	PMLL5258B	PMN50UPE
PMF63UN	PMLL5234B	PMLL5259B	PMN70XPE
PMF77XN	PMLL5235B	PMLL5260B	PMN80XP
PMF780SN	PMLL5236B	PMLL5261B	PMP4201G

Multisim 14.0 Base Components

PMP4201V	PMPB29XPE	PMST5551	PMV32UP
PMP4201Y	PMPB33XN	PMST6428	PMV33UPE
PMP4501G	PMPB33XP	PMST6429	PMV37EN
PMP4501V	PMPB43XPE	PMSTA05	PMV40UN
PMP4501Y	PMPB47XP	PMSTA06	PMV45EN
PMP5201G	PMR280UN	PMSTA42	PMV48XP
PMP5201V	PMR290UNE	PMSTA55	PMV50UPE
PMP5201Y	PMR290XN	PMSTA56	PMV60EN
PMP5501G	PMR370XN	PMSTA92	PMV65UN
PMP5501V	PMR400UN	PMT200EN	PMV65XP
PMP5501Y	PMR670UPE	PMT21EN	PMV90EN
PMPB10XNE	PMR780SN	PMT29EN	PMZ1000UN
PMPB11EN	PMSS3904	PMT760EN	PMZ250UN
PMPB12UN	PMSS3906	PMV117EN	PMZ270XN
PMPB13XNE	PMST2222	PMV160UP	PMZ350XN
PMPB15XN	PMST2222A	PMV16UN	PMZ390UN
PMPB15XP	PMST2369	PMV170UN	PMZ760SN
PMPB16XN	PMST2907A	PMV185XN	PMZB290UN
PMPB19XP	PMST3904	PMV20XN	PMZB300XN
PMPB20EN	PMST3906	PMV213SN	PMZB350UPE
PMPB20UN	PMST4401	PMV22EN	PMZB370UNE
PMPB20XPE	PMST4403	PMV28UN	PMZB380XN
PMPB23XNE	PMST5088	PMV30UN	PMZB420UN
PMPB27EP	PMST5089	PMV30XN	PMZB670UPE
PMPB29XNE	PMST5550	PMV31XN	PMZB790SN

Multisim 14.0 Base Components

PN2222	PN4249	PN5139	PRTR5V0U2X
PN2222A	PN4250	PN5142	PTVS10VP1UP
PN2369	PN4250A	PN5179	PTVS10VP1UTP
PN2369A	PN4258	PN5910	PTVS10VS1UR
PN2484	PN4258A	PN930	PTVS10VS1UTR
PN2906	PN4274	PNS40010ER	PTVS11VP1UP
PN2906A	PN4275	POLYNOMIAL_VOLT AGE	PTVS11VP1UTP
PN2907	PN4354	POTENTIOMETER	PTVS11VS1UR
PN2907A	PN4355	POTENTIOMETER_V IRTUAL	PTVS11VS1UTR
PN3565	PN4356	POTENTIOMETER_V IRTUAL	PTVS12VP1UP
PN3638	PN4391	PROBE	PTVS12VP1UTP
PN3638A	PN4392	PROBE_BLUE	PTVS12VS1UR
PN3640	PN4393	PROBE_DIG	PTVS12VS1UTR
PN3641	PN4416	PROBE_DIG_BLUE	PTVS13VP1UP
PN3642	PN4416A	PROBE_DIG_GREEN	PTVS13VP1UTP
PN3643	PN4916	PROBE_DIG_ORAN GE	PTVS13VS1UR
PN3644	PN4917	PROBE_DIG_ORAN GE	PTVS13VS1UTR
PN3645	PN5128	PROBE_DIG_RED	PTVS14VP1UP
PN3646	PN5129	PROBE_DIG_YELLO W	PTVS14VP1UTP
PN3694	PN5133	PROBE_GREEN	PTVS14VS1UR
PN4121	PN5134	PROBE_ORANGE	PTVS14VS1UTR
PN4122	PN5135	PROBE_RED	PTVS15VP1UP
PN4141	PN5136	PROBE_YELLOW	PTVS15VP1UTP
PN4143	PN5137	PRTR5V0U1T	PTVS15VS1UR
PN4248	PN5138		PTVS15VS1UTR

Multisim 14.0 Base Components

PTVS16VP1UP	PTVS26VP1UTP	PTVS40VS1UR	PTVS58VS1UTR
PTVS16VP1UTP	PTVS26VS1UR	PTVS40VS1UTR	PTVS5V0P1UP
PTVS16VS1UR	PTVS26VS1UTR	PTVS43VP1UP	PTVS5V0P1UTP
PTVS16VS1UTR	PTVS28VP1UP	PTVS43VP1UTP	PTVS5V0S1UR
PTVS17VP1UP	PTVS28VP1UTP	PTVS43VS1UR	PTVS5V0S1UTR
PTVS17VP1UTP	PTVS28VS1UR	PTVS43VS1UTR	PTVS60VP1UP
PTVS17VS1UR	PTVS28VS1UTR	PTVS45VP1UP	PTVS60VP1UTP
PTVS17VS1UTR	PTVS30VP1UP	PTVS45VP1UTP	PTVS60VS1UR
PTVS18VP1UP	PTVS30VP1UTP	PTVS45VS1UR	PTVS60VS1UTR
PTVS18VP1UTP	PTVS30VS1UR	PTVS45VS1UTR	PTVS64VP1UP
PTVS18VS1UR	PTVS30VS1UTR	PTVS48VP1UP	PTVS64VP1UTP
PTVS18VS1UTR	PTVS33VP1UP	PTVS48VP1UTP	PTVS6V0P1UP
PTVS20VP1UP	PTVS33VP1UTP	PTVS48VS1UR	PTVS6V0P1UTP
PTVS20VP1UTP	PTVS33VS1UR	PTVS48VS1UTR	PTVS6V0S1UR
PTVS20VS1UR	PTVS33VS1UTR	PTVS51VP1UP	PTVS6V0S1UTR
PTVS20VS1UTR	PTVS36VP1UP	PTVS51VP1UTP	PTVS6V5P1UP
PTVS22VP1UP	PTVS36VP1UTP	PTVS51VS1UR	PTVS6V5P1UTP
PTVS22VP1UTP	PTVS36VS1UR	PTVS51VS1UTR	PTVS6V5S1UR
PTVS22VS1UR	PTVS36VS1UTR	PTVS54VP1UP	PTVS6V5S1UTR
PTVS22VS1UTR	PTVS3V3P1UP	PTVS54VP1UTP	PTVS7V0P1UP
PTVS24VP1UP	PTVS3V3P1UTP	PTVS54VS1UR	PTVS7V0P1UTP
PTVS24VP1UTP	PTVS3V3S1UR	PTVS54VS1UTR	PTVS7V0S1UR
PTVS24VS1UR	PTVS3V3S1UTR	PTVS58VP1UP	PTVS7V0S1UTR
PTVS24VS1UTR	PTVS40VP1UP	PTVS58VP1UTP	PTVS7V5P1UP
PTVS26VP1UP	PTVS40VP1UTP	PTVS58VS1UR	PTVS7V5P1UTP

Multisim 14.0 Base Components

PTVS7V5S1UR	PUMB4	PUMH9	PZT4401
PTVS7V5S1UTR	PUMB9	PUMT1	PZT4403
PTVS8V0P1UP	PUMD10	PUMX1	PZT651T1
PTVS8V0P1UTP	PUMD12	PUMX2	PZT651T1G
PTVS8V0S1UR	PUMD13	PUMZ1	PZT751T1
PTVS8V0S1UTR	PUMD14	PUMZ2	PZT751T1G
PTVS8V5P1UP	PUMD15	PUSH_BUTTON_DP ST	PZTA14
PTVS8V5P1UTP	PUMD18	PWM	PZTA42
PTVS8V5S1UR	PUMD19	PXT2222A	PZTA44
PTVS8V5S1UTR	PUMD2	PXT2907A	PZTA92
PTVS9V0P1UP	PUMD20	PXT4401	PZTA92T1G
PTVS9V0P1UTP	PUMD24	PXT4403	PZU10B
PTVS9V0S1UR	PUMD3	PXTA14	PZU10B1
PTVS9V0S1UTR	PUMD30	PXTA42	PZU10B1A
PULSE_CURRENT	PUMD48	PXTA92	PZU10B2
PULSE_VOLTAGE	PUMD6	PZFJ108	PZU10B2A
PUMB1	PUMD9	PZFJ109	PZU10B2L
PUMB11	PUMH1	PZFJ110	PZU10B3
PUMB13	PUMH10	PZT2222A	PZU10B3A
PUMB14	PUMH11	PZT2222AT1G	PZU10BA
PUMB19	PUMH13	PZT2907A	PZU10BL
PUMB2	PUMH2	PZT2907AT1	PZU10DB2
PUMB24	PUMH30	PZT2907AT1G	PZU11B
PUMB3	PUMH4	PZT2907AT3G	PZU11B1
PUMB30	PUMH7		PZU11B1A

Multisim 14.0 Base Components

PZU11B2	PZU13B3	PZU16B2L	PZU2.7B2L
PZU11B2A	PZU13B3A	PZU16B3	PZU2.7BA
PZU11B2L	PZU13BA	PZU16B3A	PZU2.7BL
PZU11B3	PZU13BL	PZU16BA	PZU2.7DB2
PZU11B3A	PZU13DB2	PZU16BL	PZU20B
PZU11BA	PZU14B2	PZU16DB2	PZU20B1
PZU11BL	PZU14B2A	PZU18B	PZU20B1A
PZU11DB2	PZU14B2L	PZU18B1	PZU20B2
PZU12B	PZU14DB2	PZU18B1A	PZU20B2A
PZU12B1	PZU15B	PZU18B2	PZU20B2L
PZU12B1A	PZU15B1	PZU18B2A	PZU20B3
PZU12B2	PZU15B1A	PZU18B2L	PZU20B3A
PZU12B2A	PZU15B2	PZU18B3	PZU20BA
PZU12B2L	PZU15B2A	PZU18B3A	PZU20BL
PZU12B3	PZU15B2L	PZU18BA	PZU20DB2
PZU12B3A	PZU15B3	PZU18BL	PZU22B
PZU12BA	PZU15B3A	PZU18DB2	PZU22B1
PZU12BL	PZU15BA	PZU2.4B	PZU22B1A
PZU12DB2	PZU15BL	PZU2.4BA	PZU22B2
PZU13B	PZU15DB2	PZU2.4BL	PZU22B2A
PZU13B1	PZU16B	PZU2.7B	PZU22B2L
PZU13B1A	PZU16B1	PZU2.7B1	PZU22B3
PZU13B2	PZU16B1A	PZU2.7B1A	PZU22B3A
PZU13B2A	PZU16B2	PZU2.7B2	PZU22BA
PZU13B2L	PZU16B2A	PZU2.7B2A	PZU22BL

Multisim 14.0 Base Components

PZU22DB2	PZU3.3B1	PZU3.9DB2	PZU4.7B2A
PZU24B	PZU3.3B1A	PZU30B	PZU4.7B2L
PZU24B1	PZU3.3B2	PZU30BA	PZU4.7B3
PZU24B1A	PZU3.3B2A	PZU30BL	PZU4.7B3A
PZU24B2	PZU3.3B2L	PZU33B	PZU4.7BA
PZU24B2A	PZU3.3BA	PZU33BA	PZU4.7BL
PZU24B2L	PZU3.3BL	PZU33BL	PZU4.7DB2
PZU24B3	PZU3.3DB2	PZU36B	PZU5.1B
PZU24B3A	PZU3.6B	PZU36BA	PZU5.1B1
PZU24BA	PZU3.6B1	PZU36BL	PZU5.1B1A
PZU24BL	PZU3.6B1A	PZU4.3B	PZU5.1B2
PZU24DB2	PZU3.6B2	PZU4.3B1	PZU5.1B2A
PZU27B	PZU3.6B2A	PZU4.3B1A	PZU5.1B2L
PZU27BA	PZU3.6B2L	PZU4.3B2	PZU5.1B3
PZU27BL	PZU3.6BA	PZU4.3B2A	PZU5.1B3A
PZU3.0B	PZU3.6BL	PZU4.3B2L	PZU5.1BA
PZU3.0B1	PZU3.6DB2	PZU4.3B3	PZU5.1BL
PZU3.0B1A	PZU3.9B	PZU4.3B3A	PZU5.1DB2
PZU3.0B2	PZU3.9B1	PZU4.3BA	PZU5.6B
PZU3.0B2A	PZU3.9B1A	PZU4.3BL	PZU5.6B1
PZU3.0B2L	PZU3.9B2	PZU4.3DB2	PZU5.6B1A
PZU3.0BA	PZU3.9B2A	PZU4.7B	PZU5.6B2
PZU3.0BL	PZU3.9B2L	PZU4.7B1	PZU5.6B2A
PZU3.0DB2	PZU3.9BA	PZU4.7B1A	PZU5.6B2L
PZU3.3B	PZU3.9BL	PZU4.7B2	PZU5.6B3

Multisim 14.0 Base Components

PZU5.6B3A	PZU6.8DB2	PZU9.1B1A	RB521S30T5G
PZU5.6BA	PZU7.5B	PZU9.1B2	RB751CS40
PZU5.6BL	PZU7.5B1	PZU9.1B2A	RB751S40
PZU5.6DB2	PZU7.5B1A	PZU9.1B2L	RB751S40T1G
PZU6.2B	PZU7.5B2	PZU9.1B3	RB751V40
PZU6.2B1	PZU7.5B2A	PZU9.1B3A	RC4136D
PZU6.2B1A	PZU7.5B2L	PZU9.1BA	RC4136N
PZU6.2B2	PZU7.5B3	PZU9.1BL	RC4558D
PZU6.2B2A	PZU7.5B3A	PZU9.1DB2	RC4558P
PZU6.2B2L	PZU7.5BA	QL6250-4PQ208C	RC4558Y
PZU6.2B3	PZU7.5BL	QUAD_MUX_2TO1	RC4559D
PZU6.2B3A	PZU7.5DB2	QUAD_REG	RC4559P
PZU6.2BA	PZU8.2B	R145-32.768kHz	RCJ-011-SMT
PZU6.2BL	PZU8.2B1	R26-32.768kHz	RCJ-32234
PZU6.2DB2	PZU8.2B1A	R38-32.768kHz	RD10
PZU6.8B	PZU8.2B2	R710XPT	RD11
PZU6.8B1	PZU8.2B2A	R711XPT	RD12
PZU6.8B1A	PZU8.2B2L	R712XPT	RD15
PZU6.8B2	PZU8.2B3	R714XPT	RD15SB
PZU6.8B2A	PZU8.2B3A	RB520CS3002L	RD2.0S
PZU6.8B2L	PZU8.2BA	RB520CS30L	RD2.2S
PZU6.8B3	PZU8.2BL	RB520S30	RD2.4S
PZU6.8B3A	PZU8.2DB2	RB521CS30L	RD2.7S
PZU6.8BA	PZU9.1B	RB521S30	RD3.0S
PZU6.8BL	PZU9.1B1	RB521S30T1G	RD4.7

Multisim 14.0 Base Components

RD5.1	REF02HPZ	REF195GRUZ	REF3312AIDCKR
RD5.6	REF02HSZ	REF195GS	REF3318AIDBZR
RD6.2	REF02HZ	REF196GRU	REF3318AIDCKR
RD6.8	REF02RC	REF196GRU-REEL7	REF3320AIDBZR
RD7.5	REF02RC/883C	REF196GS	REF3320AIDCKR
RD7.5SB	REF191ES	REF196GSZ	REF3325AIDBZR
RD8.2	REF191GP	REF198ES	REF3325AIDCKR
RD9.2	REF191GS	REF198FSZ	REF3330AIDBZR
REF01AJ	REF192ES	REF198GP	REF3330AIDCKR
REF01AJ/883C	REF192FS	REF198GRU	REF3333AIDBZR
REF01CJ	REF192GP	REF198GRUZ	REF3333AIDCKR
REF01CP	REF192GPZ	REF198GS	REF43FZ
REF01CPZ	REF192GRU	REF3012_SOT23_3	REF43GP
REF01CS	REF192GRUZ	REF3020_SOT23_3	REF43GPZ
REF01EZ	REF192GS	REF3025_SOT23_3	REF43GS
REF01HPZ	REF193GS	REF3033_SOT23_3	REF5010AID
REF01HS	REF193GSZ	REF3040_SOT23_3	REF5010AIDGKR
REF01HZ	REF194ES	REF3120AIDBZR	REF5010ID
REF02AJ	REF194GP	REF3212AIDBVR	REF5010IDGKR
REF02AJ/883C	REF194GSZ	REF3220AIDBVR	REF5020AID
REF02AZ	REF195ES	REF3225AIDBVR	REF5020AIDGKR
REF02CP	REF195FS	REF3230AIDBVR	REF5020ID
REF02CS	REF195GP	REF3233AIDBVR	REF5020IDGKR
REF02CZ	REF195GPZ	REF3240AIDBVR	REF5025AID
REF02EZ	REF195GRU	REF3312AIDBZR	REF5025AIDGKR

Multisim 14.0 Base Components

REF5025ID	REG_FILE_2Px4	RGP02-12E	RGP20J
REF5025IDGKR	REG_FILE_4x4	RGP02-14E	RGP25A
REF5030AID	RELAY_NC	RGP02-16E	RGP25B
REF5030AIDGKR	RELAY_NO	RGP02-18E	RGP25D
REF5030ID	RELAY_NONC	RGP02-20E	RGP25G
REF5030IDGKR	RELAY1A_VIRTUAL	RGP02-20E-E3/54	RGP25J
REF5030IDR	RELAY1B_VIRTUAL	RGP10A	RGP25K
REF5040AID	RELAY1C_VIRTUAL	RGP10B	RGP25M
REF5040AIDGKR	RESISTOR_VIRTUAL	RGP10D	RGP30A
REF5040AIDR	REVERSE_1A	RGP10G	RGP30B
REF5040ID	REVERSE_2A	RGP10J	RGP30D
REF5040IDGKR	REVERSE_3A	RGP10K	RGP30G
REF5040IDR	REVERSE_4A	RGP10M	RGP30J
REF5045AID	RGF1A	RGP10M-E3/54	RGP30K
REF5045AIDGKR	RGF1B	RGP15A	RGP30M
REF5045AIDR	RGF1D	RGP15B	R-HI-008068-2
REF5045ID	RGF1G	RGP15D	RIBBON_10H
REF5045IDGKR	RGF1J	RGP15G	RIBBON_10H_LATC H
REF5045IDR	RGF1K	RGP15J	RIBBON_10H_MNT
REF5050AID	RGF1M	RGP15K	RIBBON_10V
REF5050AIDGKR	RGL34A	RGP15M	RIBBON_10V_LATC H
REF5050AIDR	RGL34B	RGP20A	RIBBON_10V_MNT
REF5050ID	RGL34D	RGP20B	RIBBON_14H
REF5050IDGKR	RGL34G	RGP20D	
REF5050IDR	RGL34J	RGP20G	

Multisim 14.0 Base Components

RIBBON_14H_LATC H	RIBBON_24V_LATC H	RIBBON_40H_LATC H	RV4136D
RIBBON_14H_MNT	RIBBON_24V_MNT	RIBBON_40H_MNT	RV4136N
RIBBON_14V	RIBBON_26H	RIBBON_40V	RV4558D
RIBBON_14V_LATC H	RIBBON_26H_LATC H	RIBBON_40V_LATC H	RV4558P
RIBBON_14V_MNT	RIBBON_26H_MNT	RIBBON_40V_MNT	S1227-1010BQ
RIBBON_16H	RIBBON_26V	RIBBON_50H	S1227-1010BR
RIBBON_16H_LATC H	RIBBON_26V_LATC H	RIBBON_50H_LATC H	S1227-16BQ
RIBBON_16H_MNT	RIBBON_26V_MNT	RIBBON_50H_MNT	S1227-16BR
RIBBON_16V	RIBBON_30H	RIBBON_50V	S1227-33BQ
RIBBON_16V_LATC H	RIBBON_30H_LATC H	RIBBON_50V_LATC H	S1227-33BR
RIBBON_16V_MNT	RIBBON_30H_MNT	RIBBON_50V_MNT	S1227-66BQ
RIBBON_20H	RIBBON_30V	RM4136FK	S1227-66BR
RIBBON_20H_LATC H	RIBBON_30V_LATC H	RM4136J	S1B-E3/61T
RIBBON_20H_MNT	RIBBON_30V_MNT	RM4136W	S1D-E3/61T
RIBBON_20V	RIBBON_34H	RM4558JG	S1G-E3/61T
RIBBON_20V_LATC H	RIBBON_34H_LATC H	RMB4S-E3/45	S1J-E3/61T
RIBBON_20V_MNT	RIBBON_34H_MNT	RS1G-E3/5AT	S1PG-E3/84A
RIBBON_24H	RIBBON_34V	RS1K-E3/61T	S2800A
RIBBON_24H_LATC H	RIBBON_34V_LATC H	RS2D-E3/52T	S2800B
RIBBON_24H_MNT	RIBBON_34V_MNT	RS2J-E3/52T	S2800D
RIBBON_24V	RIBBON_40H	RS3D-E3/57T	S2800M
		RTD	S2G-E3/52T
			S2SA1774G
			S2SC4617G
			S3D-E3/57T

Multisim 14.0 Base Components

S3M-E3/57T	SAF-XC164TM-4F40F AA	SAF-XC888CLM-6FFA 5V AC	SAK-XC2267-56F66L AC
S4PD-M3/86A			
S5227B	SAF-XC164TM-4F40F AA	SAF-XC888CLM-6FFA 5V AC	SAK-XC2267-56F80L AC
S5227G	SAF-XC866-1FRA AB	SAF-XC888CM-6FFA 5V AC	SAK-XC2267-56F80L AC
S5227J	SAF-XC866-1FRA AB		
S5227N	SAF-XC866L-1FRA AB	SAF-XC888CM-6FFA 5V AC	SAK-XC2285M-104F80L AA
SA15AG		SAF-XC888LM-6FFA 5V AC	SAK-XC2285M-104F80L AA
SA15ARLG	SAF-XC866L-1FRA AB		
SA2M-E3/5AT	SAF-XC886-6FFA 5V AC	SAF-XC888LM-6FFA 5V AC	SAK-XC2285M-56F80L AA
SA5.0A-E3/54		SAK-C167CR-LM HA+	SAK-XC2285M-56F80L AA
SA5.0CA-E3/54	SAF-XC886-6FFA 5V AC		
SA6.0A-E3/54		SAK-C167CR-LM HA+	SAK-XC2285M-72F80L AA
SA6.0CA-E3/54	SAF-XC886CLM-6FFA 5V AC		
SA9.0CA-E3/54	SAF-XC886CLM-6FFA 5V AC	SAK-C167SR-LM HA+	SAK-XC2285M-72F80L AA
SAB-C167CR-LM HA+	SAF-XC886CM-6FFA 5V AC	SAK-C167SR-LM HA+	SAK-XC2286-56F66L AC
SAB-C167CR-LM HA+	SAF-XC886CM-6FFA 5V AC	SAK-XC2264-56F66L AC	SAK-XC2286-56F66L AC
SAB-C167SR-LM HA+	SAF-XC886LM-6FFA 5V AC	SAK-XC2264-56F66L AC	SAK-XC2286-56F80L AC
SAB-C167SR-LM HA+	SAF-XC886LM-6FFA 5V AC	SAK-XC2264-56F80L AC	SAK-XC2286-56F80L AC
SAC5.0-E3/54		SAK-XC2264-56F80L AC	SAK-XC2287-56F66L AC
SAF-C167CR-LM HA+	SAF-XC888-6FFA 5V AC		
SAF-C167CR-LM HA+	SAF-XC888-6FFA 5V AC	SAK-XC2267-56F66L AC	SAK-XC2287-56F66L AC

Multisim 14.0 Base Components

SAK-XC2287-56F80L AC	SAK-XC2786X- 96F66L AC	SAK-XC888CLM- 6FFA 5V AC	SB2H90-E3/23 SB320
SAK-XC2287-56F80L AC	SAK-XC866-1FRA AB SAK-XC866-1FRA AB	SAK-XC888CM-6FFA 5V AC	SB330
SAK-XC2287-96F66L AC	SAK-XC866L-1FRA AB	SAK-XC888CM-6FFA 5V AC	SB340 SB350
SAK-XC2287-96F66L AC	SAK-XC866L-1FRA AB	SAK-XC888LM-6FFA 5V AC	SB360
SAK-XC2287-96F80L AC	SAK-XC886-6FFA 5V AC	SAK-XC888LM-6FFA 5V AC	SB3H100-E3/54 SB520
SAK-XC2287-96F80L AC	SAK-XC886-6FFA 5V AC	SAMPLE_BEND	SB530
SAK-XC2287M- 104F80L AA	SAK-XC886CLM- 6FFA 5V AC	SAMPLE_GENERIC	SB540
SAK-XC2287M- 104F80L AA	SAK-XC886CLM- 6FFA 5V AC	SAMPLE_LOSSY	SB540-E3/54
SAK-XC2287M- 56F80L AA	SAK-XC886CM-6FFA 5V AC	SAMPLE_MICROSTR IP	SB550
SAK-XC2287M- 56F80L AA	SAK-XC886CM-6FFA 5V AC	SAMPLE_OPENEND	SB560
SAK-XC2287M- 72F80L AA	SAK-XC886LM-6FFA 5V AC	SAMPLE_RFCAP	SB560-E3/54
SAK-XC2287M- 72F80L AA	SAK-XC886LM-6FFA 5V AC	SAMPLE_RFCOIL	SBAS16DXV6T1G
SAK-XC2287M- 96F66L AC	SAK-XC888-6FFA 5V AC	SAMPLE_WAVEGUI DE	SBAS20LT1G
SAK-XC2287M- 96F66L AC	SAK-XC888-6FFA 5V AC	SB	SBAT54CLT1G
SAK-XC2766X- 96F66L AC	SAK-XC888CLM- 6FFA 5V AC	SB01-15C-TB-E	SBAV70LT1G
SAK-XC2766X- 96F66L AC	SAK-XC888-6FFA 5V AC	SB040-E3/54	SBAV70LT3G
SAK-XC2766X- 96F66L AC	SAK-XC888-6FFA 5V AC	SB05-03Q-TL-E	SBAV99LT1G
SAK-XC2786X- 96F66L AC	SAK-XC888CLM- 6FFA 5V AC	SB1003M3-TL-E	SBAV99LT3G
		SB140A-E3/54	SBAW56LT1G
		SB160-E3/54	SBAW56LT3G
		SB2H100-E3/54	SBAW56TT1G
			SBC807-16LT1G

Multisim 14.0 Base Components

SBC807-16LT3G	SBCP68T1G	SBRD8350T4G	SDTC124EET1G
SBC807-25LT1G	SBE001-TL-E	SBRD8360G	SE10PJ-M3/84A
SBC807-25LT3G	SBE002-TL-E	SBRD8360RLG	SE5534AFK
SBC807-40LT1G	SBR640CTT4G	SBRD8360T4G	SE5534AJG
SBC807-40LT3G	SBR660CTT4G	SBRD8835LG	SE5534FK
SBC817-25LT1G	SBR80520LT1G	SBRD8835LT4G	SE5534JG
SBC817-25LT3G	SBR80520LT3G	SBRS81100T3G	SEAM-40-03.0-S-06-2-A-K-TR
SBC846ALT1G	SBR835LT4G	SBRS8120T3G	SEAM-40-07.0-S-06-2-A-K-TR
SBC846BDW1T1G	SBRA8160T3G	SBRS8130LT3G	
SBC846BLT1G	SBRB1045G	SBRS8140T3G	SEMICONDUCTOR_
SBC846BLT3G	SBRB1045T4G	SBRS8190T3G	CAPACITOR_VIRTU
SBC846BPDW1T1G	SBRB1545CTG	SBRS8320T3G	AL
SBC846BPDW1T2G	SBRB1545CTT4G	SBRS8340T3G	SEMICONDUCTOR_
SBC847BDW1T1G	SBRB20200CTT4G	SBS811-TL-E	RESISTOR_VIRTUAL
SBC847BDW1T3G	SBRB2545CTG	SCH2202-TL-E	SEVEN_SEG_COM_
SBC856ALT1G	SBRB2545CTT4G	SCHMITT_TRIGGER	A
SBC856BDW1T1G	SBRD81035CTLT4G	SCR	SEVEN_SEG_COM_
SBC856BDW1T3G	SBRD81045T4G	SD05T1G	A_GREEN
SBC856BWT1G	SBRD8320G	SD12CT1G	SEVEN_SEG_COM_
SBC857BDW1T1G	SBRD8320T4G	SD12T1G	A_ORANGE
SBCP56-10T1G	SBRD8330G	SD241	SEVEN_SEG_COM_
SBCP56-16T1G	SBRD8330T4G	SD41	A_YELLOW
SBCP56-16T3G	SBRD8340G	SDTA114YET1G	SEVEN_SEG_COM_
SBCP56T1G	SBRD8340T4G	SDTC114EET1G	K
SBCP56T3G	SBRD8350G	SDTC114YET1G	SEVEN_SEG_COM_
			K_BLUE

Multisim 14.0 Base Components

SEVEN_SEG_COM_K_GREEN	SEVEN_SEG_TWO-DIGIT_COM_A_BLUE	SFH 2500 FA-Z	SFH617A-3X017T
SEVEN_SEG_COM_K_ORANGE	SEVEN_SEG_TWO-DIGIT_COM_A_GREEN	SFH 2505 FA-Z	SFH6316T
SEVEN_SEG_COM_K_YELLOW	SEVEN_SEG_TWO-DIGIT_COM_A_ORANGE	SFH6136	SFH6343T
SEVEN_SEG_DECIMAL_COM_A	SEVEN_SEG_TWO-DIGIT_COM_A_BLUE	SFH6136-X001	SFH6700
SEVEN_SEG_DECIMAL_COM_A_BLUE	SEVEN_SEG_TWO-DIGIT_COM_A_YELLOW	SFH6136-X006	SFH6700-X009
SEVEN_SEG_DECIMAL_COM_A_GREEN	SEVEN_SEG_TWO-DIGIT_COM_A_YELLOW	SFH6136-X007	SFH6701
SEVEN_SEG_DECIMAL_COM_A_ORANGE	SEVEN_SEG_TWO-DIGIT_COM_K	SFH6136-X009T	SFH6701-X007
SEVEN_SEG_DECIMAL_COM_A_YELLOW	SEVEN_SEG_TWO-DIGIT_COM_K_BLUE	SFH6136-X016	SFH6701-X009
SEVEN_SEG_DECIMAL_COM_K	SEVEN_SEG_TWO-DIGIT_COM_K_GREEN	SFH6136-X017T	SFH6702
SEVEN_SEG_DECIMAL_COM_K_BLUE	SEVEN_SEG_TWO-DIGIT_COM_K_ORANGE	SFH6136-X018	SFH6702-X006
SEVEN_SEG_DECIMAL_COM_K_GREEN	SEVEN_SEG_TWO-DIGIT_COM_K_YELLOW	SFH6136-X019T	SFH6702-X007
SEVEN_SEG_DECIMAL_COM_K_ORANGE	SFH 203 FA	SFH6156-3	SFH6702-X009T
SEVEN_SEG_DECIMAL_COM_K_YELLOW	SFH 205 F	SFH6156-3T	SFH6705
SEVEN_SEG_TWO-DIGIT_COM_A	SFH 206 K	SFH615A-3	SFH6705-X006
	SFH 213	SFH615A-3X001	SFH6705-X007
	SFH 229 FA	SFH615A-3X006	SFH6711
	SFH 2400 FA	SFH615A-3X007T	SFH6711-X007
		SFH615A-3X009T	SFH6712
		SFH615A-3X016	SFH6712-X007
		SFH615A-3X017	SFH6719
		SFH617A-3	SFH6720T
		SFH617A-3X001	SFH6721T
		SFH617A-3X006	SFH6755T
		SFH617A-3X007T	SFH6756T
		SFH617A-3X016	SFH6757T

Multisim 14.0 Base Components

SFH690CT	SLOW_1A	SM8S15AHE3/2D	SMAJ530-E3/61
SFH690C-X001T	SLOW_2A	SM8S16AHE3/2D	SMAJ6.5A-E3/61
SFT1341-E	SLOW_3A	SM8S17AHE3/2D	SMAJ60A-E3/61
SFT1341-TL-E	SLOW_4A	SM8S18AHE3/2D	SMB8J28CA-E3/52
SFT1423-E	SM05T1G	SM8S22AHE3/2D	SMBJ14A-E3/52
SFT1423-TL-E	SM12T1G	SM8S24AHE3/2D	SMBJ15CA-E3/52
SFT1440-E	SM15T150A-E3/57T	SM8S26AHE3/2D	SMBJ170A-E3/52
SFT1440-H	SM15T150CA-E3/9AT	SM8S30AHE3/2D	SMBJ188CA-E3/52
SFT1440-TL-E	SM15T18A-E3/57T	SM8S33AHE3/2D	SMBJ22A-E3/52
SFT1440-TL-H	SM15T24A-E3/9AT	SM8S36AHE3/2D	SMBJ24CA-E3/52
SGL41-40-E3/96	SM15T33A-E3/57T	SM8S43AHE3/2D	SMBJ26CA-E3/52
SHIFT_4BIDI	SM15T68A-E3/57T	SMA5J28A-E3/61	SMBJ28CA-E3/52
SHIFT_4PIPO	SM15T68CA-E3/57T	SMAJ11A-E3/61	SMBJ30A-E3/52
SHIFT_8PIN	SM3G45	SMAJ11CA-E3/61	SMBJ33A-E3/52
SHIFT_8POUT	SM3J45	SMAJ12A-E3/61	SMBJ33CA-E3/52
SI2302DS	SM5S20AHE3/2D	SMAJ12CA-E3/61	SMBJ36A-E3/52
SI2304DS	SM5S22AHE3/2D	SMAJ150CA-E3/61	SMBJ36CA-E3/52
SJ1-3515N	SM5S26AHE3/2D	SMAJ15A-E3/61	SMBJ3V3-E3/52
SL05T1G	SM5S33AHE3/2D	SMAJ16A-E3/61	SMBJ45A-E3/52
SL12-E3/5AT	SM5S36AHE3/2D	SMAJ24A-E3/61	SMBJ48A-E3/52
SL13-E3/61T	SM6S33AHE3/2D	SMAJ24CA-E3/61	SMBJ48CA-E3/52
SL22-E3/52T	SM6T12A-E3/52	SMAJ26A-E3/61	SMBJ5.0CA-E3/52
SL23-E3/52T	SM8S12AHE3/2D	SMAJ28CA-E3/61	SMBJ58A-E3/52
SL43-E3/57T	SM8S14AHE3/2D	SMAJ36A-E3/61	SMBJ58CA-E3/52
SL44-E3/57T		SMAJ40CA-E3/61	SMBJ6.0A-E3/52

Multisim 14.0 Base Components

SMBJ70A-E3/52	SMCJ48CA-E3/57T	SMF6.0AT1G	SML4755
SMBJ8.0A-E3/52	SMCJ5.0CA-E3/57T	SMF6.5AT1G	SML4756
SMBJ8.0CA-E3/52	SMCJ51CA-E3/57T	SMF7.0AT1G	SML4757
SMBJ85A-E3/52	SMCJ58A-E3/57T	SMF7.5AT1G	SML4758
SMBT2222A	SMCJ6.5A-E3/57T	SMF8.0AT1G	SML4759
SMBT2907A	SMCJ75A-E3/57T	SML4735	SML4760
SMBT35200MT1G	SMCJ78A-E3/57T	SML4736	SML4761
SMBT3906	SMCJ8.5A-E3/57T	SML4737	SML4762
SMBT3946DW1T1G	SMF05CT1G	SML4738	SML4763
SMBTA06	SMF05CT2G	SML4739	SMMBD2837LT1G
SMBTA42	SMF12AT1G	SML4740	SMMBD301LT3G
SMBTA56C	SMF12CT1G	SML4741	SMMBD7000LT1G
SMBTA92	SMF15CT1G	SML4742	SMMBD7000LT3G
SMCJ12A-E3/57T	SMF18AT1G	SML4743	SMMBD914LT1G
SMCJ130CA-E3/57T	SMF22AT1G	SML4744	SMMBD914LT3G
SMCJ15A-E3/57T	SMF24AT1G	SML4745	SMMBT2222ALT1G
SMCJ15CA-E3/57T	SMF24CT1G	SML4746	SMMBT2222ALT3G
SMCJ16CA-E3/57T	SMF26AT1G	SML4747	SMMBT2369ALT1G
SMCJ18A-E3/57T	SMF28AT1G	SML4748	SMMBT2907ALT1G
SMCJ18CA-E3/57T	SMF30AT1G	SML4749	SMMBT2907ALT3G
SMCJ26CA-E3/57T	SMF33AT1G	SML4750	SMMBT3904LT1G
SMCJ28CA-E3/57T	SMF36AT1G	SML4751	SMMBT3904TT1G
SMCJ30CA-E3/57T	SMF48AT1G	SML4752	SMMBT4401LT1G
SMCJ33CA-E3/57T	SMF5.0AT1G	SML4753	SMMBT4403LT1G
SMCJ36CA-E3/57T	SMF58AT1G	SML4754	SMMBT5401LT1G

Multisim 14.0 Base Components

SMMBT5551LT1G	SMMUN2211LT3G	SMUN5114DW1T1 G	SMUN5233T1G
SMMBT5551LT3G	SMMUN2213LT1G	SMUN5114T1G	SMUN5235DW1T1 G
SMMBTA06LT1G	SMMUN2213LT3G	SMUN5115DW1T1 G	SMUN5237DW1T1 G
SMMBTA06LT3G	SMMUN2214LT1G	SMUN5115T1G	SMUN5311DW1T2 G
SMMBTA06WT1G	SMMUN2215LT1G	SMUN5116DW1T1 G	SMUN5312DW1T1 G
SMMBTA14LT1G	SMMUN2216LT1G	SMUN5133T1G	SMUN5313DW1T1 G
SMMBTA42LT1G	SMMUN2216LT3G	SMUN5211T1G	SMUN5314DW1T1 G
SMMBTA42LT3G	SMMUN2233LT1G	SMUN5211T3G	SMUN5315DW1T1 G
SMMBTA56LT1G	SMMUN2234LT1G	SMUN5212T1G	SMUN5330DW1T1 G
SMMBTA56LT3G	SMS05T1G	SMUN5213DW1T1 G	SMUN5335DW1T1 G
SMMBTA92LT1G	SMUN2111T1G	SMUN5214DW1T1 G	SN10502D
SMMBTA92LT3G	SMUN2111T3G	SMUN5214T1G	SN10502DGK
SMMDL914T1G	SMUN2114T1G	SMUN5215T1G	SN10502DGN
SMMJT350T1G	SMUN2211T1G	SMUN5216DW1T1 G	SN200501036DRE4
SMMSD301T1G	SMUN2211T3G	SMUN5230DW1T1 G	SN412008DRE4
SMMSD4148T1G	SMUN2216T1G	SMUN5232DW1T1 G	SN7002N
SMMSD4148T3G	SMUN2230T1G	SMUN5232T1G	SN7002W
SMMUN2111LT1G	SMUN2232T1G	SMUN5233DW1T1 G	SNSS30201MR6T1G
SMMUN2111LT3G	SMUN2240T1G		SNSS35200MR6T1G
SMMUN2113LT1G	SMUN5112DW1T1 G		
SMMUN2114LT1G	SMUN5112T1G		
SMMUN2116LT1G	SMUN5113DW1T1 G		
SMMUN2116LT3G			
SMMUN2134LT1G	SMUN5113T1G		
SMMUN2211LT1G			

Multisim 14.0 Base Components

SNSS40600CF8T1G	SPP15P10P H	SR_FF_NEGSR	SS2H10-E3/2CT
SONALERT	SPP15P10PL H	SR_FF_POSSR	SS2P3L-M3/84A
SPB08P06P G	SPP18P06P H	SR_LATCH	SS2P4-M3/84A
SPB100N03S2-03 G	SPP80P06P H	SR_LATCH_NEGSR	SS2PH10-M3/84A
SPB18P06P G	SPST	SS0503SH-TL-E	SS32
SPB80P06P G	SPST_CLOSED	SS10P3-M3/86A	SS32-E3/57T
SPD04P10PL G	SPST_NC_DB	SS10P4-M3/86A	SS33
SPD08P06P G	SPST_NC_SB	SS10P6-M3/86A	SS34
SPD09P06PL G	SPST_NO_DB	SS10PH10-M3/86A	SS34-E3/57T
SPD15P10P G	SPST_NO_SB	SS14-E3/61T	SS35
SPD15P10PL G	SPST_OPEN	SS16-E3/61T	SS36-E3/57T
SPD18P06P G	SPZT2222AT1G	SS16T3G	SS3P4HM3/84A
SPD30N03S2L-07 G	SPZT2907AT1G	SS1H10-E3/5AT	SS3P4LHM3/86A
SPD30N03S2L-10 G	SPZT651T1G	SS1P3L-M3/84A	SS3P6-E3/84A
SPD30N03S2L-20 G	SR_4BIDI	SS1P4L-M3/84A	SS5P10-M3/86A
SPD30P06P G	SR_4P_P_3SO	SS1P4-M3/84A	SS5P6-M3/86A
SPD50N03S2-07 G	SR_4P_P_INV	SS1P6L-E3/84A	SS8P3L-M3/86A
SPD50N03S2L-06 G	SR_4S_P	SS22T3G	SS8PH10-M3/86A
SPD50P03L G	SR_8P_2S	SS24-E3/52T	SSA24-E3/61T
SPDT	SR_8P_S	SS24S-E3/61T	SSA33L-E3/61T
SPDT_CLOSED	SR_8P_S_C	SS24T3	SSA34-E3/61T
SPDT_OPEN	SR_8PS_S_AS_L	SS24T3G	SSC53L-E3/57T
SPEED_F	SR_8PS_S_SL	SS26-E3/52T	SSC54-E3/57T
SPEED_FR	SR_8S_P	SS26T3	SSM2017P
SPP08P06P H	SR_FF	SS26T3G	SSM2017S

Multisim 14.0 Base Components

SSM2135S	SUR81560G	SURS8105T3G	SZ1SMA5927BT3G
SSM2212RZ	SUR83020PTG	SURS8110T3G	SZ1SMA5932BT3G
SSM2212RZ-R7	SUR83060PTG	SURS8115T3G	SZ1SMA5936BT3G
SSM2212RZ-RL	SUR8820G	SURS8120T3G	SZ1SMA5940BT3G
SSRD8620CTRG	SUR8840G	SURS8140T3G	SZ1SMB14AT3G
SSRD8620CTT4G	SURA8110T3G	SURS8160T3G	SZ1SMB24AT3G
SSRD8620CTT4RG	SURA8120T3G	SURS8205T3G	SZ1SMB24CAT3G
ST10F168- PQFP(144)	SURA8130T3G	SURS8210T3G	SZ1SMB26CAT3G
	SURA8140T3G	SURS8220T3G	SZ1SMB28AT3G
ST10F269T3- TQFP(144)	SURA8160T3G	SURS8320T3G	SZ1SMB28CAT3G
	SURA8210T3G	SURS8340T3G	SZ1SMB30AT3G
ST10R272L- TQFP(100)	SURA8215T3G	SURS8360BT3G	SZ1SMB30CAT3G
	SURA8220T3G	SURS8360T3G	SZ1SMB33CAT3G
ST7263B-SDIP(32)	SURA8240T3G	SZ1.5SMC15AT3G	SZ1SMB5.0AT3G
ST7263B-SO(34)	SURB1620CTT4G	SZ1.5SMC20AT3G	SZ1SMB58CAT3G
STD110N02RT4G	SURD8320T4G	SZ1.5SMC33AT3G	SZ1SMB5918BT3G
STD24N06LT4G	SURD8330T4G	SZ1.5SMC39AT3G	SZ1SMB5919BT3G
STD2955T4G	SURD8530T4G	SZ1.5SMC43AT3G	SZ1SMB5920BT3G
STD5406NT4G	SURHB8840CTT4G	SZ1.5SMC62AT3G	SZ1SMB5921BT3G
STD5407NT4G	SURHD8560T4G	SZ1SMA30AT3G	SZ1SMB5922BT3G
STEP_CURRENT	SURHD8560W1T4G	SZ1SMA40CAT3G	SZ1SMB5924BT3G
STEP_VOLTAGE	SURHS8160T3G	SZ1SMA5913BT3G	SZ1SMB5925BT3G
STP32N06L	SURS340DT3G	SZ1SMA5918BT3G	SZ1SMB5927BT3G
SUR620CTT4G	SURS360DBT3G	SZ1SMA5921BT3G	SZ1SMB5931BT3G
SUR81520G	SURS360DT3G	SZ1SMA5922BT3G	SZ1SMB5933BT3G

Multisim 14.0 Base Components

SZ1SMB5934BT3G	SZBZX84C75LT1G	SZMM5Z27VT1G	SZMMBZ5231BLT1 G
SZ1SMB5935BT3G	SZBZX84C9V1LT1G	SZMM5Z36VT1G	SZMMBZ5231BLT3 G
SZ1SMB5936BT3G	SZBZX84C9V1LT3G	SZMM5Z3V0T1G	SZMMBZ5232BLT1 G
SZ1SMB5937BT3G	SZESD5Z5.0T1G	SZMM5Z3V3T1G	SZMMBZ5240BLT1 G
SZ1SMB5939BT3G	SZESD5Z7.0T1G	SZMM5Z4V7ST1G	SZMMBZ5242BLT1 G
SZ1SMC36AT3G	SZESD9B5.0ST5G	SZMM5Z4V7ST5G	SZMMBZ5248BLT1 G
SZBZX84B16LT1G	SZMM3Z10VT1G	SZMM5Z5V1T1G	SZMMBZ5254BLT1 G
SZBZX84C12LT1G	SZMM3Z12VST1G	SZMM5Z5V6ST1G	SZMMBZ5256BLT1 G
SZBZX84C15LT1G	SZMM3Z15VT1G	SZMM5Z5V6T1G	SZMMBZ5256BLT1 G
SZBZX84C15LT3G	SZMM3Z18VT1G	SZMM5Z6V2ST1G	SZMMBZ5256BLT1 G
SZBZX84C33LT1G	SZMM3Z20VT1G	SZMM5Z6V8ST1G	SZMMBZ5256BLT1 G
SZBZX84C33LT3G	SZMM3Z2V4T1G	SZMM5Z6V8T1G	SZMMBZ5256BLT1 G
SZBZX84C36LT1G	SZMM3Z3V3ST1G	SZMM5Z7V5T1G	SZMMBZ5V6ALT1G
SZBZX84C3V0LT1G	SZMM3Z3V6T1G	SZMM5Z8V2ST1G	SZMMQA15VT1G
SZBZX84C4V7LT1G	SZMM3Z43VT1G	SZMM5Z8V2T1G	SZMMQA5V6T1G
SZBZX84C4V7LT3G	SZMM3Z4V3ST1G	SZMMBZ15VDLT1G	SZMMQA6V2T1G
SZBZX84C5V1LT1G	SZMM3Z4V7T1G	SZMMBZ15VDLT3G	SZMMSZ10T1G
SZBZX84C5V1LT3G	SZMM3Z5V1T1G	SZMMBZ20VALT1G	SZMMSZ12T1G
SZBZX84C5V6LT1G	SZMM3Z5V6ST1G	SZMMBZ27VALT1G	SZMMSZ2V7T1G
SZBZX84C5V6LT3G	SZMM5Z10VT1G	SZMMBZ27VALT3G	SZMMSZ3V3T1G
SZBZX84C68LT1G	SZMM5Z12VT1G	SZMMBZ27VCLT1G	SZMMSZ4678T1G
SZBZX84C6V2LT1G	SZMM5Z16VT1G	SZMMBZ33VALT1G	SZMMSZ4683T1G
SZBZX84C6V2LT3G	SZMM5Z18VT1G	SZMMBZ5221BLT1 G	SZMMSZ4688T1G
SZBZX84C6V8LT1G	SZMM5Z20VT1G	SZMMBZ5222BLT1 G	SZMMSZ4689T1G
SZBZX84C6V8LT3G	SZMM5Z24VT1G		

Multisim 14.0 Base Components

SZMMSZ4690T1G	SZMMSZ5258BT3G	TC1410COA	TC1411VPA
SZMMSZ4690T3G	SZMMSZ5259BT1G	TC1410CPA	TC1411VUA
SZMMSZ4691T1G	SZMMSZ5260BT1G	TC1410EOA	TC1412COA
SZMMSZ4692T1G	SZMMSZ5262BT1G	TC1410EPA	TC1412CPA
SZMMSZ4696T1G	SZMSQA6V1W5T2G	TC1410EUA	TC1412EOA
SZMMSZ4699T1G	SZNUP1105LT1G	TC1410NCOA	TC1412EPA
SZMMSZ4705T1G	SZNUP1301ML3T1G	TC1410NCPA	TC1412EUA
SZMMSZ4715T1G	SZNUP2105LT1G	TC1410NEOA	TC1412NCOA
SZMMSZ5221BT1G	SZNUP4301MR6T1 G	TC1410NEPA	TC1412NCPA
SZMMSZ5225BT1G		TC1410NEUA	TC1412NEOA
SZMMSZ5226BT1G	SZNUP4304MR6T1 G	TC1410NVUA	TC1412NEPA
SZMMSZ5228BT1G	SZNZ9F2V7ST5G	TC1411COA	TC1412NEUA
SZMMSZ5231BT1G	SZNZ9F6V2ST5G	TC1411CPA	TC4404COA
SZMMSZ5234BT1G	SZP6SMB15AT3G	TC1411EOA	TC4404CPA
SZMMSZ5235BT1G	SZP6SMB18AT3G	TC1411EPA	TC4404EOA
SZMMSZ5236BT1G	SZP6SMB20AT3G	TC1411EUA	TC4404EPA
SZMMSZ5239BT1G	SZP6SMB33AT3G	TC1411NCOA	TC4405COA
SZMMSZ5240BT1G	SZP6SMB43CAT3G	TC1411NCPA	TC4405CPA
SZMMSZ5242BT1G	SZP6SMB51AT3G	TC1411NEOA	TC4405EOA
SZMMSZ5242BT3G	SZP6SMB6.8AT3G	TC1411NEPA	TC4405EPA
SZMMSZ5243BT1G	SZP6SMB62AT3G	TC1411NEUA	TC4420CAT
SZMMSZ5245BT1G	SZSMF12CT1G	TC1411NVOA	TC4420COA
SZMMSZ5246BT1G	SZSMF33AT1G	TC1411NVPA	TC4420CPA
SZMMSZ5254BT1G	T_FF	TC1411NVUA	TC4420EMF
SZMMSZ5258BT1G	T_FF_NEGSR	TC1411VOA	TC4420EOA

Multisim 14.0 Base Components

TC4420EPA	TC4422VPA	TC4424VPA	TC4427COA
TC4420IJA	TC4423AVMF	TC4425AVMF	TC4427CPA
TC4420MJA	TC4423AVOA	TC4425AVOA	TC4427EMF
TC4420VAT	TC4423AVOE	TC4425AVOE	TC4427EOA
TC4420VMF	TC4423AVPA	TC4425AVPA	TC4427EPA
TC4420VOA	TC4423COE	TC4425COE	TC4427EUA713
TC4420VPA	TC4423CPA	TC4425CPA	TC4427VMF
TC4421AVMF	TC4423EOE	TC4425EOE	TC4427VOA
TC4421CAT	TC4423EPA	TC4425EPA	TC4427VUA
TC4421CPA	TC4423MJA	TC4425VMF	TC4428ACOA713
TC4421EMF713	TC4423VMF	TC4425VOE	TC4428AEJA
TC4421EPA	TC4423VOE	TC4425VPA	TC4428AEOA713
TC4421ESM	TC4423VPA	TC4426ACOA713	TC4428AMJA
TC4421MJA	TC4424AVMF	TC4426AEOA713	TC4428COA
TC4421VAT	TC4424AVOA	TC4426COA	TC4428CPA
TC4421VMF	TC4424AVOE	TC4426CPA	TC4428EMF
TC4421VPA	TC4424AVPA	TC4426EMF	TC4428EOA
TC4422CAT	TC4424COE	TC4426EOA	TC4428EPA
TC4422CPA	TC4424CPA	TC4426EPA	TC4428EUA
TC4422EAT	TC4424EMF	TC4426EUA	TC4428VMF
TC4422EPA	TC4424EOE	TC4426MJA	TC4428VOA
TC4422ESM	TC4424EPA	TC4426VMF	TC4428VUA
TC4422MJA	TC4424MJA	TC4426VUA	TC4429COA713
TC4422VAT	TC4424VMF	TC4427ACOA713	TC4429EMF
TC4422VMF	TC4424VOE	TC4427AEOA713	TC4429EOA713

Multisim 14.0 Base Components

TC4429IJA	TC4452VPA	TDE1891_ZIP11	TDZ3V9J
TC4429MJA	TC4467COE	TDE1897C_DIP8	TDZ4V3J
TC4429VAT	TC4467CPD	TDE1897C_SO20	TDZ4V7J
TC4429VMF	TC4467EOE713	TDE1898C_DIP8	TDZ5V1J
TC4429VOA	TC4468COE	TDE1898C_SIP9	TDZ5V6J
TC4429VPA	TC4468CPD	TDE1898C_SO20	TDZ6V2J
TC4431COA	TC4468EOE713	TDM_CURRENT	TDZ6V8J
TC4431CPA	TC4468MOE	TDM_VOLTAGE	TDZ7V5J
TC4431EOA	TC4469COE	TDZ10J	TDZ8V2J
TC4431EPA	TC4469CPD	TDZ11J	TDZ9V1J
TC4431VOA	TC4469EJD	TDZ12J	TEMD1000
TC4431VPA	TC4469MJD	TDZ13J	TEMD1020
TC4432COA	TCET1100	TDZ15J	TEMD1030
TC4432CPA	TCET1100G	TDZ16J	TEMD5010X01
TC4432EOA	TCET1600	TDZ18J	TEMD5020X01
TC4432EPA	TCET1600G	TDZ20J	TEMD5110X01
TC4432VOA	TCLT1003	TDZ22J	TEMD5510FX01
TC4432VPA	TCMT1103	TDZ24J	TEMD6010FX01
TC4451VAT	TCMT1600	TDZ27J	TEMP_NC
TC4451VMF	TCMT4600	TDZ2V4J	TEMP_NO
TC4451VOA	TD_SW1	TDZ2V7J	TEMPLATE_1P1S_T MODEL
TC4451VPA	TDA2030	TDZ30J	TEMPLATE_1P2S_C OUPLED
TC4452VAT	TDE1890_SO20	TDZ3V0J	TEMPLATE_1P2S_N ON_LINEAR
TC4452VMF	TDE1890_ZIP11	TDZ3V3J	
TC4452VOA	TDE1891_SIP11	TDZ3V6J	

Multisim 14.0 Base Components

TEMPLATE_1P2S_T	THS3095DDA	THS3201DBVT	THS4031IDGN
AP_TMODEL	THS3110DGN	THS3201DGK	THS4031MFK
TEMPLATE_1P2S_T MODEL	THS3110ID	THS3202D	THS4031MJG
TEST_LABEL	THS3110IDGN	THS3202DGK	THS4032CD
TEST_PT_SMT	THS3110IDR	THS3202DGN	THS4032CDGN
TEST_PT_THT	THS3111CD	THS4001CD	THS4032ID
THERMAL_NOISE	THS3111CDGNR	THS4001ID	THS4032IDGN
THERMAL_OL	THS3111DGN	THS4011CD	THS4041CD
THERMAL_OL_RELAY	THS3111ID	THS4011CDGN	THS4041CDGN
	THS3111IDGN	THS4011ID	THS4041ID
THREE_PHASE_DELTA	THS3120CDGN	THS4011MFKB	THS4041IDGN
THREE_PHASE_WYE	THS3120DGN	THS4012CD	THS4042CD
THS3001CD	THS3120ID	THS4012CDGN	THS4042CDGN
THS3001CDGN	THS3120IDGN	THS4012ID	THS4042ID
THS3001ID	THS3121CD	THS4021CD	THS4042IDGN
THS3001IDGN	THS3121ID	THS4021CDGN	THS4051CD
THS3061D	THS3121IDGN	THS4021ID	THS4051CDGN
THS3061DGN	THS3122CD	THS4021IDGN	THS4051ID
THS3062D	THS3122CDDA	THS4022CD	THS4051IDGN
THS3062DDA	THS3122ID	THS4022CDGN	THS4051MFK
THS3062DGN	THS3122IDDA	THS4022ID	THS4051MJG
THS3091D	THS3125CPWP	THS4022IDGN	THS4052CD
THS3091DDA	THS3125ID	THS4031CD	THS4052CDGN
THS3095D	THS3125IPWP	THS4031CDGN	THS4052ID
	THS3201D	THS4031ID	THS4052IDGN

Multisim 14.0 Base Components

THS4061CD	THS4130IDGK	THS4215DGK	THS4304DBVT
THS4061CDGN	THS4131CD	THS4215DGN	THS4304DGK
THS4061ID	THS4131CDGK	THS4215DRBT	THS4500CD
THS4061IDGN	THS4131ID	THS4221D	THS4500CDGK
THS4061MFK	THS4131IDGK	THS4221DBV	THS4500CDGN
THS4061MJG	THS4140CD	THS4221DGK	THS4500ID
THS4062CD	THS4140CDGK	THS4221DGN	THS4500IDGK
THS4062CDGN	THS4140ID	THS4222D	THS4500IDGN
THS4062ID	THS4140IDGK	THS4222DGK	THS4501CD
THS4062IDGN	THS4141CD	THS4222DGN	THS4501CDGK
THS4081CD	THS4141CDGK	THS4225D	THS4501CDGN
THS4081CDGN	THS4141ID	THS4225DGK	THS4501ID
THS4081ID	THS4141IDGK	THS4225DGN	THS4501IDGK
THS4081IDGN	THS4150CD	THS4226DGQ	THS4501IDGN
THS4082CD	THS4150CDGK	THS4271D	THS4502CD
THS4082CDGN	THS4150ID	THS4271DGK	THS4502CDGK
THS4082ID	THS4150IDGK	THS4271DGN	THS4502ID
THS4082IDGN	THS4151CD	THS4271DR	THS4502IDGK
THS4120CD	THS4151CDGK	THS4271DRBT	THS4503CD
THS4120CDGK	THS4151ID	THS4281D	THS4503CDGK
THS4121CD	THS4151IDGK	THS4281DBVR	THS4503CDGN
THS4121CDGK	THS4211D	THS4281DGK	THS4503ID
THS4130CD	THS4211DGK	THS4302RGTT	THS4503IDGK
THS4130CDGK	THS4211DGN	THS4303RGTT	THS4503IDGN
THS4130ID	THS4215D	THS4304D	THS4505D

Multisim 14.0 Base Components

THS4505DGK	THS6042IDDA	THS6093IPWP	TIP100G
THS4508RGTR	THS6043CD	THS6182D	TIP101G
THS4509RGT	THS6043CPWP	THS6182DW	TIP102G
THS4511RGTT	THS6043ID	THS6182DWP	TIP106G
THS4513RGTR	THS6043IPWP	THS6182RHFR	TIP107G
THS4520RGTR	THS6052CD	THS7001CPWP	TIP110G
THS4601CD	THS6052CDDA	THS7001IPWP	TIP111G
THS4601CDDA	THS6052ID	THS7002CPWP	TIP112G
THS4601CDG4	THS6052IDDA	THS7002IPWP	TIP115G
THS4601ID	THS6053CPWPR	THS7530PWP	TIP116G
THS4601IDDA	THS6053ID	TIME_DELAY_1A	TIP117G
THS4601IDG4	THS6053IPWP	TIME_DELAY_1C	TIP120G
THS4631D	THS6062CD	TIME_DELAY_2A	TIP121G
THS4631DDA	THS6062CDGN	TIME_DELAY_2C	TIP122G
THS4631DGN	THS6062ID	TIME_DELAY_3A	TIP125G
THS6002CDWP	THS6062IDGN	TIME_DELAY_3C	TIP126G
THS6002IDWP	THS6072CD	TIME_DELAY_4A	TIP127G
THS6007IPWP	THS6072CDGN	TIME_DELAY_4C	TIP140G
THS6012CDWP	THS6072ID	TIME_DELAY_NC	TIP141G
THS6012IDWP	THS6072IDGNR	TIME_DELAY_NO	TIP142G
THS6012IGQER	THS6092CDDA	TIMED_NCTC	TIP147G
THS6022CPWP	THS6092ID	TIMED_NCTO	TIP2955G
THS6022IPWP	THS6092IDDA	TIMED_NOTC	TIP29AG
THS6042CDDA	THS6093CPWP	TIMED_NOTO	TIP29BG
THS6042ID	THS6093ID	TI-MSP430-HDR	TIP29CG

Multisim 14.0 Base Components

TIP3055G	TIS92	TL032ACP	TL034CD
TIP30CG	TIS93	TL032AID	TL034CN
TIP31AG	TIS97	TL032AIP	TL034ID
TIP31BG	TIS98	TL032AMD	TL034IN
TIP31CG	TIS99	TL032AMFK	TL034MD
TIP31G	TL022CD	TL032AMJG	TL034MFK
TIP32AG	TL022CP	TL032AMJL	TL034MJ
TIP32BG	TL022MJG	TL032AMP	TL034MN
TIP32CG	TL022MU	TL032CD	TL044CJ
TIP32G	TL031ACD	TL032CP	TL044CN
TIP33CG	TL031ACP	TL032ID	TL044MFK
TIP35AG	TL031AID	TL032IP	TL044MJ
TIP35CG	TL031AIP	TL032MD	TL044MW
TIP36AG	TL031AMD	TL032MFK	TL051ACD
TIP36CG	TL031AMFK	TL032MJG	TL051ACP
TIP41AG	TL031AMJG	TL032ML	TL051AID
TIP41BG	TL031AML	TL032MP	TL051AIP
TIP41CG	TL031AMP	TL034ACD	TL051AMD
TIP42AG	TL031ID	TL034ACN	TL051AMFK
TIP42BG	TL031IP	TL034AID	TL051AMJG
TIP42CG	TL031MD	TL034AIN	TL051AML
TIP42G	TL031MFK	TL034AMD	TL051AMP
TIP47G	TL031MJG	TL034AMFK	TL051CD
TIP48G	TL031MP	TL034AMJ	TL051CP
TIP50G	TL032ACD	TL034AMN	TL051ID

Multisim 14.0 Base Components

TL051IP	TL054ACN	TL061ML	TL064CN
TL051MD	TL054AID	TL061MU	TL064CNSR
TL051MFK	TL054AIN	TL061VD	TL064CPW
TL051MJG	TL054AMD	TL061VP	TL064ID
TL051ML	TL054AMFK	TL062ACD	TL064IN
TL051MP	TL054AMJ	TL062ACP	TL064MFK
TL052ACD	TL054AMN	TL062ACPSR	TL064MJ
TL052ACP	TL054CD	TL062BCD	TL064MW
TL052AID	TL054CN	TL062BCP	TL066ACD
TL052AIP	TL054ID	TL062CD	TL066ACP
TL052AMD	TL054IN	TL062CP	TL066CD
TL052AMFK	TL054MD	TL062CPSR	TL066CP
TL052AMJG	TL054MFK	TL062CPW	TL066ID
TL052AML	TL054MJ	TL062ID	TL066IP
TL052AMP	TL054MN	TL062IP	TL066MFK
TL052CD	TL061ACD	TL062IPW	TL066MJG
TL052CP	TL061ACP	TL062MFK	TL070ACD
TL052ID	TL061BCD	TL062MJG	TL070ACJG
TL052IP	TL061BCP	TL062ML	TL070ACP
TL052MD	TL061CD	TL062MU	TL070CD
TL052MFK	TL061CP	TL064ACD	TL070CJG
TL052MJG	TL061ID	TL064ACN	TL070CP
TL052ML	TL061IP	TL064BCD	TL070CPW
TL052MP	TL061MFK	TL064BCN	TL070ID
TL054ACD	TL061MJG	TL064CD	TL070IJG

Multisim 14.0 Base Components

TL070IP	TL072CPW	TL080CP	TL082MFK
TL070MD	TL072CPWLE	TL080M	TL082MJG
TL070MP	TL072ID	TL081ACD	TL083
TL071ACD	TL072IP	TL081ACJG	TL084ACD
TL071ACJG	TL072MFK	TL081ACP	TL084ACN
TL071ACP	TL072MJG	TL081AMJG	TL084ACNSR
TL071BCD	TL072MJGB	TL081BCD	TL084BCD
TL071BCP	TL072ML	TL081BCJG	TL084BCN
TL071CD	TL072MP	TL081BCP	TL084CD
TL071CJG	TL074ACD	TL081CD	TL084CN
TL071CP	TL074ACN	TL081CJG	TL084CNSR
TL071CPWLE	TL074BCD	TL081CP	TL084CPW
TL071ID	TL074BCN	TL081CPW	TL084ID
TL071IP	TL074CD	TL081ID	TL084IN
TL071MFK	TL074CN	TL081IJG	TL084MFK
TL071MJG	TL074CPWLE	TL081IP	TL084MJ
TL071ML	TL074ID	TL081MFK	TL085
TL072ACD	TL074IN	TL081MJG	TL087CD
TL072ACP	TL074MFK	TL081MU	TL087CJG
TL072ACPSR	TL074MJ	TL082CD	TL087CL
TL072BCD	TL074MN	TL082CM	TL087CP
TL072BCP	TL074MW	TL082CP	TL087ID
TL072CD	TL075	TL082ID	TL087IJG
TL072CP	TL075CN	TL082IP	TL087IL
TL072CPSR	TL080CD	TL082IPWR	TL087IP

Multisim 14.0 Base Components

TL088CD	TL321CP	TL35071P	TLC081IP
TL088CJG	TL321ID	TL431ACD	TLC1078CD
TL088CL	TL321IP	TL431ACLP	TLC1078CP
TL088CP	TL322CD	TL431ACP	TLC1078ID
TL088ID	TL322CDR	TL431BCD	TLC1078IP
TL088IJG	TL322CP	TL431BCLP	TLC1078MD
TL088IL	TL322ID	TL431BCP	TLC1078MFK
TL088IP	TL322IP	TL972ID	TLC1078MJG
TL088MJG	TL33071D	TL972IDGKR	TLC1078MP
TL088ML	TL33071P	TL972IP	TLC1079CD
TL088MU	TL331IDBVR	TL972IPW	TLC1079CN
TL136	TL331KDBVR	TLC070CD	TLC1079ID
TL136N	TL34071D	TLC070CP	TLC1079IN
TL287CD	TL34071P	TLC070ID	TLC1079MD
TL287CJG	TL3472CD	TLC070IP	TLC1079MFK
TL287CL	TL3472CP	TLC071CD	TLC1079MJ
TL287CP	TL3472ID	TLC071CP	TLC1079MN
TL288CD	TL3472IP	TLC071ID	TLC2201ACD
TL288CJG	TL3474CD	TLC071IP	TLC2201ACP
TL288CL	TL3474CN	TLC074CD	TLC2201AID
TL288CP	TL3474CPW	TLC074CN	TLC2201AIP
TL288MJG	TL3474ID	TLC074CPWP	TLC2201BCD
TL288ML	TL3474IN	TLC081CD	TLC2201BCP
TL288MU	TL3474IPW	TLC081CP	TLC2201BID
TL321CD	TL35071D	TLC081ID	TLC2201BIP

Multisim 14.0 Base Components

TLC2201CD	TLC2202Y	TLC2264CPWLE	TLC251CP
TLC2201CP	TLC2252AID	TLC2264MFK	TLC251Y
TLC2201ID	TLC2252AIP	TLC2264MJ	TLC252ACD
TLC2201IP	TLC2252AIPWLE	TLC2264MW	TLC252ACP
TLC2201MD	TLC2252CD	TLC2272ACD	TLC252ACPW
TLC2201MFK	TLC2252CP	TLC2272ACP	TLC252BCD
TLC2201MJG	TLC2252CPWLE	TLC2272CD	TLC252BCP
TLC2201MP	TLC2252MFK	TLC2272CP	TLC252BCPW
TLC2201Y	TLC2252MJG	TLC2272CPWLE	TLC252CD
TLC2202ACD	TLC2252MU	TLC2272Y	TLC252CP
TLC2202ACP	TLC2254CD	TLC2274ACD	TLC252CPW
TLC2202AID	TLC2254CN	TLC2274ACN	TLC254ACD
TLC2202AIP	TLC2254CPWLE	TLC2274ACPW	TLC254ACN
TLC2202BCD	TLC2254MFK	TLC2274CD	TLC254BCD
TLC2202BCP	TLC2254MJ	TLC2274CN	TLC254BCN
TLC2202BID	TLC2254MW	TLC2274CPWLE	TLC254CD
TLC2202BIP	TLC2262CD	TLC2274MD	TLC254CN
TLC2202CD	TLC2262CP	TLC2274MFK	TLC254CPW
TLC2202CP	TLC2262CPWLE	TLC2274MJ	TLC25L2ACD
TLC2202ID	TLC2262MFK	TLC2274MN	TLC25L2ACP
TLC2202IP	TLC2262MJG	TLC251ACD	TLC25L2BCD
TLC2202MD	TLC2262MU	TLC251ACP	TLC25L2BCP
TLC2202MFK	TLC2264CD	TLC251BCD	TLC25L2CD
TLC2202MJG	TLC2264CN	TLC251BCP	TLC25L2CP
TLC2202MP	TLC2264CPW	TLC251CD	TLC25L4CD

Multisim 14.0 Base Components

TLC25L4CN	TLC2652C-8D	TLC2654AMF	TLC271BCD
TLC25M2ACD	TLC2652CN	TLC2654AMFK	TLC271BCP
TLC25M2ACP	TLC2652CP	TLC2654AMJ	TLC271BID
TLC25M2BCD	TLC2652I-14D	TLC2654AMJG	TLC271BIP
TLC25M2BCP	TLC2652ID	TLC2654AMN	TLC271CD
TLC25M2CD	TLC2652IN	TLC2654AMP	TLC271CP
TLC25M2CP	TLC2652IP	TLC2654C-14D	TLC271ID
TLC25M4CD	TLC2652M-14D	TLC2654C-8D	TLC271IP
TLC25M4CN	TLC2652M-8D	TLC2654CN	TLC271MD
TLC2652AC-14D	TLC2652MFK	TLC2654CP	TLC271MFK
TLC2652AC-8D	TLC2652MJ	TLC2654I-14D	TLC271MJG
TLC2652ACN	TLC2652MJG	TLC2654I-8D	TLC271MP
TLC2652ACP	TLC2652MN	TLC2654IN	TLC272CD
TLC2652AI-14D	TLC2652MP	TLC2654IP	TLC272CP
TLC2652AI-8D	TLC2652Y	TLC2654M-14D	TLC272CPW
TLC2652AIN	TLC2654AC-14D	TLC2654M-8D	TLC272ID
TLC2652AIP	TLC2654AC-8D	TLC2654MFK	TLC272IP
TLC2652AM-14D	TLC2654ACN	TLC2654MJ	TLC272MD
TLC2652AM-8D	TLC2654ACP	TLC2654MJG	TLC272MFK
TLC2652AMFK	TLC2654AI-14D	TLC2654MN	TLC272MJG
TLC2652AMJ	TLC2654AID	TLC2654MP	TLC272MP
TLC2652AMJG	TLC2654AIN	TLC271ACD	TLC274CD
TLC2652AMN	TLC2654AIP	TLC271ACP	TLC274CN
TLC2652AMP	TLC2654AM-14D	TLC271AID	TLC274CPW
TLC2652C-14D	TLC2654AM-8D	TLC271AIP	TLC274ID

Multisim 14.0 Base Components

TLC274IN	TLC27L2BCD	TLC27L4MFK	TLC27M2BID
TLC274MD	TLC27L2BCP	TLC27L4MJ	TLC27M2BIP
TLC274MFK	TLC27L2BID	TLC27L4MN	TLC27M2CD
TLC274MJ	TLC27L2BIP	TLC27L7CD	TLC27M2CP
TLC274MN	TLC27L2CD	TLC27L7CP	TLC27M2ID
TLC277CD	TLC27L2CP	TLC27L7ID	TLC27M2IP
TLC277CP	TLC27L2ID	TLC27L7IP	TLC27M2MD
TLC277ID	TLC27L2IP	TLC27L7MD	TLC27M2MFK
TLC277IP	TLC27L2MD	TLC27L7MFK	TLC27M2MJG
TLC277MD	TLC27L2MFK	TLC27L7MJG	TLC27M2MP
TLC277MFK	TLC27L2MJG	TLC27L7MP	TLC27M4ACD
TLC277MJG	TLC27L2MP	TLC27L9CD	TLC27M4ACN
TLC277MP	TLC27L4ACD	TLC27L9CN	TLC27M4AID
TLC279CD	TLC27L4ACN	TLC27L9ID	TLC27M4AIN
TLC279CN	TLC27L4AID	TLC27L9IN	TLC27M4BCD
TLC279ID	TLC27L4AIN	TLC27L9MD	TLC27M4BCN
TLC279IN	TLC27L4BCD	TLC27L9MFK	TLC27M4BID
TLC279MD	TLC27L4BCN	TLC27L9MJ	TLC27M4BIN
TLC279MFK	TLC27L4BID	TLC27L9MP	TLC27M4CD
TLC279MJ	TLC27L4BIN	TLC27M2ACD	TLC27M4CN
TLC279MN	TLC27L4CD	TLC27M2ACP	TLC27M4ID
TLC27L2ACD	TLC27L4CN	TLC27M2AID	TLC27M4IN
TLC27L2ACP	TLC27L4ID	TLC27M2AIP	TLC27M4MD
TLC27L2AID	TLC27L4IN	TLC27M2BCD	TLC27M4MFK
TLC27L2AIP	TLC27L4MD	TLC27M2BCP	TLC27M4MJ

Multisim 14.0 Base Components

TLC27M4MN	TLC352CD	TLC3704MFK	TLC393CD
TLC27M7CD	TLC352CP	TLC3704MJ	TLC393CP
TLC27M7CP	TLC352ID	TLC3704QJ	TLC393ID
TLC27M7ID	TLC352IP	TLC372CD	TLC393IP
TLC27M7IP	TLC352MFK	TLC372CP	TLC393MD
TLC27M7MD	TLC352MJG	TLC372CPW	TLC393MFK
TLC27M7MFK	TLC354CD	TLC372ID	TLC393MJG
TLC27M7MJG	TLC354CN	TLC372IP	TLC393MP
TLC27M7MP	TLC354CPW	TLC372MD	TLC551CD
TLC27M9CD	TLC354ID	TLC372MFK	TLC551CP
TLC27M9CN	TLC354IN	TLC372MJG	TLC552CD
TLC27M9ID	TLC354MD	TLC372MP	TLC552CN
TLC27M9IN	TLC354MN	TLC372QD	TLC555CD
TLC27M9MD	TLC3702CD	TLC372QP	TLC555CP
TLC27M9MFK	TLC3702CP	TLC374CD	TLC555CPSR
TLC27M9MJ	TLC3702ID	TLC374CN	TLC555CPW
TLC27M9MN	TLC3702IP	TLC374CPW	TLC555ID
TLC339CD	TLC3702MFK	TLC374ID	TLC555IP
TLC339CN	TLC3702MJG	TLC374IN	TLC555QDR
TLC339ID	TLC3702QJG	TLC374MD	TLC556CD
TLC339IN	TLC3704CD	TLC374MFK	TLC556CN
TLC339MD	TLC3704CN	TLC374MJ	TLC556ID
TLC339MN	TLC3704CPW	TLC374MN	TLC556IN
TLC339QD	TLC3704ID	TLC374QD	TLE2021ACD
TLC339QN	TLC3704IN	TLC374QN	TLE2021ACP

Multisim 14.0 Base Components

TLE2021AID	TLE2022BID	TLE2024CN	TLE2027MP
TLE2021AIP	TLE2022BIP	TLE2024IDW	TLE2037ACD
TLE2021AMD	TLE2022CD	TLE2024IN	TLE2037ACP
TLE2021AMFK	TLE2022CDBLE	TLE2024MDW	TLE2037AID
TLE2021AMJG	TLE2022CP	TLE2024MFK	TLE2037AIP
TLE2021AMP	TLE2022CPWLE	TLE2024MJ	TLE2037AMD
TLE2021BI	TLE2022ID	TLE2024MN	TLE2037AMFK
TLE2021BMJG	TLE2022IP	TLE2024Y	TLE2037AMJG
TLE2021CD	TLE2022Y	TLE2027ACD	TLE2037AML
TLE2021CDBLE	TLE2024ACDW	TLE2027ACP	TLE2037AMP
TLE2021CP	TLE2024ACN	TLE2027AID	TLE2037CD
TLE2021CPWLE	TLE2024AIDW	TLE2027AIP	TLE2037CP
TLE2021ID	TLE2024AIN	TLE2027AMD	TLE2037ID
TLE2021IP	TLE2024AMDW	TLE2027AMFK	TLE2037IP
TLE2021MD	TLE2024AMFK	TLE2027AMJG	TLE2037MD
TLE2021MFK	TLE2024AMJ	TLE2027AML	TLE2037MFK
TLE2021MJG	TLE2024AMN	TLE2027AMP	TLE2037MJG
TLE2021MP	TLE2024BCDW	TLE2027CD	TLE2037ML
TLE2021Y	TLE2024BCN	TLE2027CP	TLE2037MP
TLE2022ACD	TLE2024BIDW	TLE2027ID	TLE2061ACD
TLE2022ACP	TLE2024BIN	TLE2027IP	TLE2061ACL
TLE2022AID	TLE2024BMDW	TLE2027MD	TLE2061ACP
TLE2022AIP	TLE2024BMJ	TLE2027MFK	TLE2061AID
TLE2022BCD	TLE2024BMN	TLE2027MJG	TLE2061AIL
TLE2022BCP	TLE2024CDW	TLE2027ML	TLE2061AIP

Multisim 14.0 Base Components

TLE2061AMD	TLE2062ACD	TLE2064ACD	TLE2072CD
TLE2061AMFK	TLE2062ACP	TLE2064ACN	TLE2072CP
TLE2061AMJG	TLE2062AID	TLE2064AID	TLE2072MFK
TLE2061AML	TLE2062AIP	TLE2064AIN	TLE2074CN
TLE2061AMP	TLE2062AMD	TLE2064AMD	TLE2081CD
TLE2061BCL	TLE2062AMFK	TLE2064AMFK	TLE2081CP
TLE2061BIL	TLE2062AMJG	TLE2064AMJ	TLE2081MFK
TLE2061BIP	TLE2062AMP	TLE2064AMN	TLE2081MJG
TLE2061BMJG	TLE2062BCD	TLE2064BCN	TLE2082ACD
TLE2061BML	TLE2062BCP	TLE2064BIN	TLE2082ACP
TLE2061BMP	TLE2062BID	TLE2064BMJ	TLE2082AID
TLE2061CD	TLE2062BIP	TLE2064BMN	TLE2082AIP
TLE2061CDBLE	TLE2062BMD	TLE2064CD	TLE2082AMD
TLE2061CL	TLE2062BMFK	TLE2064CN	TLE2082AMFK
TLE2061CP	TLE2062BMJG	TLE2064ID	TLE2082AMJG
TLE2061CPWLE	TLE2062BMP	TLE2064IN	TLE2082AMP
TLE2061ID	TLE2062CD	TLE2064MD	TLE2082CD
TLE2061IL	TLE2062CP	TLE2064MFK	TLE2082CP
TLE2061IP	TLE2062ID	TLE2064MJ	TLE2082ID
TLE2061MD	TLE2062IP	TLE2064MN	TLE2082IP
TLE2061MFK	TLE2062MD	TLE2064Y	TLE2082MD
TLE2061MJG	TLE2062MFK	TLE2071CD	TLE2082MFK
TLE2061ML	TLE2062MJG	TLE2071CP	TLE2082MJG
TLE2061MP	TLE2062MP	TLE2071MFK	TLE2082MP
TLE2061Y	TLE2062Y	TLE2071MJG	TLE2084CN

Multisim 14.0 Base Components

TLE2141ACD	TLE2142CD	TLE2161AID	TLE2237CDW
TLE2141ACP	TLE2142CP	TLE2161AIP	TLE2237CP
TLE2141AID	TLE2142ID	TLE2161AMD	TLE2425CD
TLE2141AIP	TLE2142IP	TLE2161AMFK	TLE2425ID
TLE2141AMD	TLE2142MD	TLE2161AMJG	TLE2426CD
TLE2141AMFK	TLE2142MFK	TLE2161AML	TLE2426IP
TLE2141AMJG	TLE2142MJG	TLE2161AMP	TL-OP
TLE2141AMP	TLE2142MP	TLE2161BCP	TL-OP1
TLE2141CD	TLE2142Y	TLE2161BIP	TLV2211CDBV
TLE2141CP	TLE2144ACN	TLE2161BMJ	TLV2211IDBV
TLE2141ID	TLE2144AIN	TLE2161BML	TLV2221CDBV
TLE2141IP	TLE2144AMFK	TLE2161BMP	TLV2221IDBV
TLE2141MD	TLE2144AMJ	TLE2161CD	TLV2231CDBV
TLE2141MFK	TLE2144AMN	TLE2161CP	TLV2231IDBV
TLE2141MJG	TLE2144CDW	TLE2161ID	TLV2252ID
TLE2141MP	TLE2144CN	TLE2161IP	TLV2252IP
TLE2141Y	TLE2144IDW	TLE2161MD	TLV2252MFK
TLE2142ACD	TLE2144IN	TLE2161MFK	TLV2252MJG
TLE2142ACP	TLE2144MDW	TLE2161MJG	TLV2252MU
TLE2142AID	TLE2144MFK	TLE2161ML	TLV2254AID
TLE2142AIP	TLE2144MJ	TLE2161MP	TLV2254AIN
TLE2142AMD	TLE2144MN	TLE2227ACP	TLV2254AIPWLE
TLE2142AMFK	TLE2144Y	TLE2227CDW	TLV2254ID
TLE2142AMJG	TLE2161ACD	TLE2227CP	TLV2254IN
TLE2142AMP	TLE2161ACP	TLE2237ACP	TLV2254MFK

Multisim 14.0 Base Components

TLV2254MJ	TLV2341ID	TLV2370IP	TLV2402IP
TLV2254QD	TLV2341IP	TLV2371ID	TLV2432AID
TLV2262AIPWLE	TLV2341IPWLE	TLV2371IDBV	TLV2432AIPW
TLV2262ID	TLV2342ID	TLV2371IP	TLV2432AMJG
TLV2262IP	TLV2342IP	TLV2372ID	TLV2434AID
TLV2262MFK	TLV2342IPWLE	TLV2372IDGK	TLV2434AIPW
TLV2262MJG	TLV2344ID	TLV2372IP	TLV2442CD
TLV2262MU	TLV2344IN	TLV2373ID	TLV2442CPW
TLV2264AIPWLE	TLV2344IPWLE	TLV2373IDGS	TLV2442MJG
TLV2264ID	TLV2352ID	TLV2373IN	TLV2444CD
TLV2264IN	TLV2352IP	TLV2374ID	TLV2444CPW
TLV2264MJ	TLV2352IPW	TLV2374IN	TLV2444ID
TLV2264QD	TLV2354ID	TLV2374IPW	TLV2444IPW
TLV2322ID	TLV2354IN	TLV2375ID	TLV2450AID
TLV2322IP	TLV2354IPW	TLV2375IN	TLV2450AIP
TLV2322IPWLE	TLV2354MJ	TLV2375IPW	TLV2451AID
TLV2324ID	TLV2361CDBV	TLV2401CD	TLV2451AIP
TLV2324IN	TLV2361IDBV	TLV2401CDBV	TLV2452AID
TLV2324IPWLE	TLV2362ID	TLV2401ID	TLV2452AIP
TLV2332ID	TLV2362IDGK	TLV2401IDBV	TLV2453AID
TLV2332IP	TLV2362IP	TLV2401IP	TLV2453AIN
TLV2332IPWLE	TLV2362IPS	TLV2402CD	TLV2454AID
TLV2334ID	TLV2362IPW	TLV2402CDGK	TLV2454AIN
TLV2334IN	TLV2370ID	TLV2402ID	TLV2454AIPW
TLV2334IPWLE	TLV2370IDBV	TLV2402IDGK	TLV2455AID

Multisim 14.0 Base Components

TLV2455AIN	TLV271IDBVR	TLV2764IN	TLV3401IP
TLV2455AIPW	TLV271IP	TLV2764IPW	TLV342ID
TLV2460CD	TLV272CD	TLV2765ID	TLV342IDGKR
TLV2460CDBV	TLV272CDGK	TLV2765IN	TLV342IRUGR
TLV2460CP	TLV272ID	TLV2765IPW	TLV3501AID
TLV2461CD	TLV272IDGK	TLV2772CD	TLV3501AIDBVR
TLV2461CDBV	TLV272IP	TLV2772CDGK	TLV3691IDCKR
TLV2461CP	TLV274CD	TLV2772CP	TLV3691IDPFR
TLV2470AID	TLV274CPW	TLV2782AID	TLV3701CD
TLV2470AIP	TLV274ID	TLV2783AID	TLV3701CDBVR
TLV2471AID	TLV274IN	TLV2784AID	TLV3701ID
TLV2471AIP	TLV274IPW	TLV2784AIPW	TLV3701IDBVR
TLV2472AID	TLV2760ID	TLV2785AID	TLV3701IP
TLV2472AIP	TLV2760IDBV	TLV2785AIPW	TLV4110ID
TLV2473AID	TLV2760IP	TLV3012AIDBVR	TLV4110IDGNR
TLV2473AIP	TLV2761ID	TLV3012AIDCKR	TLV4110IP
TLV2474AID	TLV2761IDBV	TLV3201AIDBVR	TLV4111CD
TLV2474AIN	TLV2761IP	TLV3201AIDCKR	TLV4111CDGN
TLV2474AIPWP	TLV2762ID	TLV3202AID	TLV4111ID
TLV2475AID	TLV2762IDGK	TLV3202AIDGK	TLV4111IDGN
TLV2475AIN	TLV2762IP	TLV3401CD	TLV4112CD
TLV2475AIPWP	TLV2763ID	TLV3401CDBVR	TLV4112CDGN
TLV271CD	TLV2763IDGS	TLV3401ID	TLV4112CP
TLV271CDBVR	TLV2763IN	TLV3401IDBVR	TLV4112ID
TLV271ID	TLV2764ID	TLV3401IDG4	TLV4112IDGN

Multisim 14.0 Base Components

TLV4112IP	TN2219	TPS2838_SO16	TPSMC36A/9AT
TLV4113CDGQR	TN2219A	TPS2839_SO16	TPSMC39A-E3/57T
TLV4113ID	TN2905	TPS2848_SO14	TPSMP18AHM3/84A
TLV4113IDGQ	TN2905A	TPS2849_SO14	A
TLV4113IN	TN4036	TPS5300_SO32	TPSMP24AHM3/84A
TMP90C800F	TOSHIBA-MIPS-HDR	TPS60240_SO8	A
TMP90C800N	TPS2811_SO8	TPS60241_SO8	TPSMP27AHE3/84A
TMP90C801F	TPS2812_SO8	TPS60242_SO8	TPSMP30AHM3/84A
TMP90C801N	TPS2813_SO8	TPS60243_SO8	A
TMP94CM40F	TPS2814_SO8	TPSMA16AHE3/61T	TPSMP36AHM3/84A
TMS320C6711B-100GFNA	TPS2815_SO8	TPSMA20A/11T	TRANSFER_FUNCTION_BLOCK
TMS320LC2402A-PAG(64)	TPS2816_SOT23_5	TPSMA27AHE3/61T	TRANSISTOR
TMS320LC2402A-PG(64)	TPS2817_SOT23_5	TPSMA30AHE3/61T	TRANSISTOR_DELAY
TMS320LC2402A-PZ(100)	TPS2818_SOT23_5	TPSMA33AHE3/61T	TRANSISTOR_DIODE
TMS320LC2404A-PZ(100)	TPS2819_SOT23_5	TPSMA36AHE3/5AT	E
TMS320LC2406A-PZ(100)	TPS2828_SOT23_5	TPSMB24AHE3/52T	TRANSISTOR_DIODE_DELAY
TMS320LF2402A-PG(64)	TPS2829_SOT23_5	TPSMB27A/2	TRANSPORT_DELAY
TMS320LF2403A-PAG(64)	TPS2830_SO14	TPSMB30AHE3/52T	TRF37A75IDSGR
TMS320LF2403A-PZ(100)	TPS2831_SO14	TPSMB33AHE3/52T	TRF37B75IDSGR
TMS320LF2406A-PZ(100)	TPS2832_SO8	TPSMB36A/5T	TRF37C75IDSGR
TMS320LF2407A-PGE(144)	TPS2833_SO8	TPSMB39A-E3/2T	TRIAC
	TPS2834_SO14	TPSMC22A-E3/57T	TRIANGULAR_CURRENT
	TPS2835_SO14	TPSMC27A-E3/57T	ENT
	TPS2836_SO8	TPSMC30AHE3_A/H	TRIANGULAR_VOLTAGE
	TPS2837_SO8	TPSMC33A-E3/51T	

Multisim 14.0 Base Components

TRIODE_VIRTUAL	UA709MJ	UC2705_DIP8	UC3842T_SO8
TRISTATE	UA709MU	UC2842A_DIP8	UC3843A_DIP8
TRISTATE_NEG	UA709MW	UC2842A_SO8	UC3843A_SO8
TS_VIRTUAL	UA723CD	UC2842B_DIP8	UC3843B_DIP8
TVP5145PFP- TQFP(80)	UA723CFK	UC2842B_SO8	UC3843B_SO8
	UA723CJ	UC2843A_DIP8	UC3843T_DIP8
U257	UA723CN	UC2843A_SO8	UC3843T_SO8
U308	UA723MU	UC2843B_DIP8	UC3844A_DIP8
U309	UA741CD	UC2843B_SO8	UC3844A_SO8
U310	UA741CP	UC2844A_DIP8	UC3844B_DIP8
U401	UA741MFK	UC2844A_SO8	UC3844B_SO8
U402	UA741MJ	UC2844B_DIP8	UC3844T_DIP8
U403	UA741MJG	UC2844B_SO8	UC3844T_SO8
U404	UA741MU	UC2845A_DIP8	UC3845A_DIP8
U405	UA747CD	UC2845A_SO8	UC3845A_SO8
U406	UA747CN	UC2845B_DIP8	UC3845B_DIP8
U440	UA747MFK	UC2845B_SO8	UC3845B_SO8
U441	UA747MJ	UC3248	UC3845T_DIP8
UA709AMJ	UA747MW	UC3705_DIP8	UC3845T_SO8
UA709AMJG	UA748CD	UC3842	UCC27323_SO8
UA709AMU	UA748CP	UC3842A_DIP8	UCC27324_SO8
UA709AMW	UA748JG	UC3842A_SO8	UCC27325_SO8
UA709CD	UA748MJG	UC3842B_DIP8	UCC37323_SO8
UA709CJG	UA748MU	UC3842B_SO8	UCC37324_SO8
UA709CP	UC1705_DIP8	UC3842T_DIP8	UCC37325_SO8

Multisim 14.0 Base Components

UF4002-E3/54	V_REF3	VDD	VO2631-X006
UF4007-E3/54	V_REF4	VEE	VO2631-X007T
UF5406-E3/54	V_REF5	VN10LF	VO2631-X017T
UG06D-E3/54	V10P10-M3/86A	VO0600T	VO4661
UG1D-E3/54	V12P10-M3/86A	VO0601T	VO4661-X006
UG30DPT-E3/45	V8P10HM3/86A	VO0601-X001T	VO4661-X007T
UG5JT-E3/45	VARIABLE_CAPACIT OR	VO0611T	VO615A-3
UG8DT-E3/45		VO0630T	VO615A-3X001
UG8JCT-E3/45	VARIABLE_CAPACIT OR_VIRTUAL	VO0631T	VO615A-3X006
UG8JT-E3/45	VARIABLE_INDUCT OR	VO0631-X001T	VO615A-3X007T
ULN2001_DIP16		VO0661T	VO615A-3X008T
ULN2001_SO16	VARIABLE_INDUCT OR_VIRTUAL	VO2601	VO615A-3X009T
ULN2002_DIP16		VO2601-X006	VO615A-3X016
ULN2002_SO16	VARIABLE_PULLUP_ VIRTUAL	VO2601-X007T	VO615A-3X017T
ULN2003_DIP16	VARIABLE_RESISTO R_VIRTUAL	VO2601-X016	VO615A-3X018T
ULN2003_SO16		VO2601-X017T	VO615A-3X019T
ULN2004_DIP16	VBP104FAS	VO2611	VOLTAGE_CONTRO LLED_CAPACITOR_ VIRTUAL
ULN2004_SO16	VBP104FASR	VO2611-X006	
UNDCD_BARGRAPH	VBPW34FAS	VO2611-X007T	VOLTAGE_CONTRO LLED_CURRENT_SO URCE
US1G-E3/61T	VBPW34FASR	VO2611-X016	
US1J-E3/5AT	VBPW34S	VO2611-X017T	
US1M-E3/61T	VBPW34SR	VO2630	VOLTAGE_CONTRO LLED_DPDT
UX60-MB-5ST	VCC	VO2630-X006	VOLTAGE_CONTRO LLED_INDUCTOR_VI RTUAL
V_REF1	VDAC	VO2630-X007T	
V_REF2	VDAC16	VO2631	

Multisim 14.0 Base Components

VOLTAGE_CONTROLLED_LIMITER	VOLTAGE_INTEGRATOR	XC3142A-VQ100	XC5204-4PQ100C
		XC3142L-VQ100	XC5204-4TQ144C
VOLTAGE_CONTROLLED_PIECEWISE_LINEAR_SOURCE	VOLTAGE_LIMITER	XC4002XL-1PC84C	XC5204-5PC84C
	VOLTAGE_SLEW_RATE_BLOCK	XC4002XL-2PC84C	XC5204-5PQ100C
VOLTAGE_CONTROLLED_RESISTOR_VIRTUAL	VOLTAGE_SUMMER	XC4002XL-3PC84C	XC5204-5TQ144C
	VOLTMETER_H	XC5202-3PC84C	XC5204-6PC84C
VOLTAGE_CONTROLLED_SINE_WAVE	VOLTMETER_HR	XC5202-3PQ100C	XC5204-6PQ100C
	VOLTMETER_V	XC5202-3TQ144C	XC5204-6TQ144C
VOLTAGE_CONTROLLED_SPDT	VOLTMETER_VR	XC5202-3VQ64C	XC5206-3PC84C
	VOM452T	XC5202-4PC84C	XC5206-3PQ100C
VOLTAGE_CONTROLLED_SPST	VOM453T	XC5202-4PQ100C	XC5206-3TQ144C
	VSS	XC5202-4TQ144C	XC5206-4PC84C
VOLTAGE_CONTROLLED_SPST_ANIMATED	W06G-E4/51	XC5202-4VQ64C	XC5206-4PQ100C
	WOBBLE_STICK	XC5202-5PC84C	XC5206-4TQ144C
VOLTAGE_CONTROLLED_SQUARE_WAVE	XC3020A-PQ100	XC5202-5PQ100C	XC5206-5PC84C
	XC3030A-PQ100	XC5202-5TQ144C	XC5206-5PQ100C
VOLTAGE_CONTROLLED_TRIANGLE_WAVE	XC3030A-VQ100	XC5202-5VQ64C	XC5206-5TQ144C
	XC3030L-VQ100	XC5202-6PC84C	XC5206-6PC84C
VOLTAGE_CONTROLLED_VOLTAGE_SOURCE	XC3042A-PQ100	XC5202-6PQ100C	XC5206-6PQ100C
	XC3042A-VQ100	XC5202-6TQ144C	XC5206-6TQ144C
VOLTAGE_DIFFERENTIATOR	XC3042L-VQ100	XC5202-6VQ64C	XC5210-3PC84C
	XC3120A-PQ100	XC5204-3PC84C	XC5210-3TQ144C
VOLTAGE_GAIN_BLOCK	XC3130A-PQ100	XC5204-3PQ100C	XC5210-4PC84C
	XC3130A-VQ100	XC5204-3TQ144C	XC5210-4TQ144C
VOLTAGE_HYSTeresis_BLOCK	XC3142A-PQ100	XC5204-4PC84C	XC5210-5PC84C

Multisim 14.0 Base Components

XC5210-5TQ144C	XILINX-PARALLEL- IV-HDR	XOR6	Z4KE190A
XC5210-6PC84C		XOR7	Z4KE200
XC5210-6TQ144C	XNOR2	XOR7	Z4KE200A
XC5215-3PQ160C	XNOR2	XOR8	Z80180-DIP(64)
XC5215-4PQ160C	XNOR3	XOR8	Z80180-PLCC(68)
XC5215-5PQ160C	XNOR3	Z08470-DIP(40)	Z80180-QFP(80)
XC5215-6PQ160C	XNOR4	Z4KE100	Z80181-QFP(100)
XC9572XL- 10TQ100C	XNOR4	Z4KE100A	Z80182-QFP(100)
XC9572XL-7TQ100C	XNOR5	Z4KE110	Z80182-VQFP(100)
XCS05-3PC84C	XNOR5	Z4KE110A	Z80195-QFP(100)
XCS05-4PC84C	XNOR6	Z4KE120	Z84015-QFP(100)
XCS05XL-4PC84C	XNOR6	Z4KE120A	Z84C00-DIP(40)
XCS10-3PC84C	XNOR7	Z4KE130	Z84C00-PLCC(44)
XCS10-4PC84C	XNOR7	Z4KE130A	Z84C00-QFP(44)
XCS10XL-4PC84C	XNOR8	Z4KE140	Z84C10-DIP(40)
XCS20-3VQ100C	XNOR8	Z4KE140A	Z84C10-PLCC(44)
XCS20-4VQ100C	XOR2	Z4KE150	Z84C15-QFP(100)
XCS20XL-4VQ100C	XOR2	Z4KE150A	Z84C15-VQFP(100)
XCS30-3VQ100C	XOR3	Z4KE160	Z84C20-DIP(40)
XCS30-4VQ100C	XOR3	Z4KE160A	Z84C20-PLCC(44)
XCS30XL-4VQ100C	XOR4	Z4KE170	Z84C30-DIP(28)
XCS40-4PQ208C	XOR4	Z4KE170A	Z84C30-PLCC(44)
XCS40XL-4PQ208C	XOR5	Z4KE180	Z84C30-QFP(44)
XILINX-PARALLEL- III-IV-HDR	XOR5	Z4KE180A	Z84C40-DIP(40)
	XOR6	Z4KE190	Z84C41-DIP(40)

Multisim 14.0 Base Components

Z84C42-DIP(40)	ZC835A	ZPD20	ZTX108
Z84C43-QFP(44)	ZC836A	ZPD22	ZTX108B
Z84C44-PLCC(44)	ZDX1F	ZPD24	ZTX109
Z84C90-LQFP(100)	ZDX2F	ZPD27	ZTX109B
Z84C90-PLCC(84)	ZDX5	ZPD3.0	ZTX212
Z8L180-DIP(64)	ZENER	ZPD3.3	ZTX212A
Z8L180-PLCC(68)	ZGL41_100	ZPD3.6	ZTX213
Z8L180-QFP(80)	ZGL41_110	ZPD3.9	ZTX213A
Z8L182-QFP(100)	ZGL41_120	ZPD30	ZTX214
Z8L182-VQFP(100)	ZGL41_130	ZPD33	ZTX214A
Z8S180-DIP(64)	ZGL41_140	ZPD4.3	ZTX237
Z8S180-PLCC(68)	ZGL41_150	ZPD4.7	ZTX237B
Z8S180-QFP(80)	ZGL41_160	ZPD5.1	ZTX238
ZC820	ZGL41_170	ZPD6.2	ZTX238B
ZC821	ZGL41_180	ZPD6.8	ZTX239
ZC822	ZGL41_190	ZPD7.5	ZTX239B
ZC823	ZGL41_200	ZPD8.2	ZTX320
ZC824	ZPD10	ZTX1047A	ZTX321
ZC825	ZPD11	ZTX1048A	ZTX325
ZC826	ZPD12	ZTX1049A	ZTX327
ZC830A	ZPD13	ZTX1051A	ZTX337A
ZC831A	ZPD15	ZTX1053A	ZTX338A
ZC832A	ZPD16	ZTX1055A	ZTX360
ZC833A	ZPD18	ZTX107	ZTX450
ZC834A	ZPD2.7	ZTX107B	ZTX454

Multisim 14.0 Base Components

ZTX455	ZTX749	ZVN0124A
ZTX458	ZTX750	ZVN2106A
ZTX549	ZTX751	ZVN2106G
ZTX550	ZTX753	ZVN3306A
ZTX558	ZTX757	ZVN3306F
ZTX601B	ZTX758	ZVN3310F
ZTX604	ZTX788A	ZVN4210G
ZTX605	ZTX788B	ZVN4306G
ZTX614	ZTX789A	ZVN4310G
ZTX618	ZTX790A	ZVN4424G
ZTX649	ZTX792A	ZVP2106A
ZTX650	ZTX795A	ZVP2106G
ZTX651	ZTX796A	ZVP3306
ZTX653	ZTX849	ZVP4424A
ZTX657	ZTX851	
ZTX658	ZTX869	
ZTX688B	ZTX948	
ZTX689B	ZTX949	
ZTX690B	ZTX951	
ZTX692B	ZTX953	
ZTX694B	ZTX955	
ZTX696B	ZTX956	
ZTX704	ZTX957	
ZTX705	ZTX958	
ZTX718	ZTX968	