

Multisim 14.1 Education Components

0 Ohm [CAT10-000J4LF]	0 Ohm [CR0805-J/-000ELF]	1 kOhm [4114R-2-102]	1 kOhm [4306M-102-102]
0 Ohm [CAT16-000J2GLF]	0 Ohm [CR0805-J/-000GLF]	1 kOhm [4114R-2-102LF]	1 kOhm [4306M-102-102LF]
0 Ohm [CAT16-000J2LF]	0 Ohm [CR1206-J/-000ELF]	1 kOhm [4116R-1-102]	1 kOhm [4306R-101-102]
0 Ohm [CAT16-000J4GLF]	0 Ohm [CR1206-J/-000GLF]	1 kOhm [4116R-1-102LF]	1 kOhm [4306R-101-102LF]
0 Ohm [CAT16-000J4LF]	0 Ohm [CR2010-J/-000ELF]	1 kOhm [4116R-2-102]	1 kOhm [4306R-102-102]
0 Ohm [CAT16-000J8LF]	0 Ohm [CR2512-J/-000ELF]	1 kOhm [4116R-2-102LF]	1 kOhm [4306R-102-102LF]
0 Ohm [CAY10-000J2LF]	0 Ohm [PWR6327WR000JE]	1 kOhm [4304M-101-102]	1 kOhm [4308H-101-102]
0 Ohm [CAY10-000J4LF]	0.5_AMP	1 kOhm [4304M-101-102LF]	1 kOhm [4308H-101-102LF]
0 Ohm [CAY16-000J2LF]	02BZ2.2	1 kOhm [4304M-102-102]	1 kOhm [4308H-102-102]
	02DZ4.7		
0 Ohm [CAY16-000J4LF]	05AZ2.2	1 kOhm [4304M-102-102LF]	1 kOhm [4308H-102-102LF]
0 Ohm [CAY16-000J8LF]	1 kOhm [4108R-1-102LF]	1 kOhm [4306H-101-102]	1 kOhm [4308M-101-102]
0 Ohm [CR0201-J/-000GLF]	1 kOhm [4108R-2-102]	1 kOhm [4306H-101-102LF]	1 kOhm [4308M-101-102LF]
0 Ohm [CR0402-J/-000GLF]	1 kOhm [4108R-2-102LF]	1 kOhm [4306H-102-102]	1 kOhm [4308M-102-102]
0 Ohm [CR0603-J/-000ELF]	1 kOhm [4114R-1-102]	1 kOhm [4306M-101-102]	1 kOhm [4308M-102-102LF]
0 Ohm [CR0603-J/-000GLF]	1 kOhm [4114R-1-102LF]	1 kOhm [4306M-101-102LF]	1 kOhm [4308R-101-102]

Multisim 14.1 Education Components

1 kOhm [4308R-101-102LF]	1 kOhm [4310R-102-102]	1 kOhm [4420P-T01-102]	1 kOhm [4606X-AP1-102LF]
1 kOhm [4308R-102-102]	1 kOhm [4310R-102-102LF]	1 kOhm [4420P-T02-102]	1 kOhm [4606X-AP2-102LF]
1 kOhm [4308R-102-102LF]	1 kOhm [4311R-101-102]	1 kOhm [4420P-T02-102LF]	1 kOhm [4607X-101-102LF]
1 kOhm [4309R-101-102]	1 kOhm [4311R-101-102LF]	1 kOhm [4604H-101-102LF]	1 kOhm [4608H-101-102LF]
1 kOhm [4309R-101-102LF]	1 kOhm [4416P-1-102]	1 kOhm [4604X-101-102LF]	1 kOhm [4608H-102-102LF]
1 kOhm [4310H-101-102]	1 kOhm [4416P-1-102LF]	1 kOhm [4604X-102-102LF]	1 kOhm [4608M-101-102LF]
1 kOhm [4310H-101-102LF]	1 kOhm [4416P-2-102]	1 kOhm [4605M-101-102LF]	1 kOhm [4608M-102-102LF]
1 kOhm [4310H-102-102]	1 kOhm [4416P-2-102LF]	1 kOhm [4605X-101-102LF]	1 kOhm [4608X-101-102LF]
1 kOhm [4310H-102-102LF]	1 kOhm [4416P-T01-102]	1 kOhm [4605X-AP1-102LF]	1 kOhm [4608X-102-102LF]
1 kOhm [4310M-101-102]	1 kOhm [4416P-T01-102LF]	1 kOhm [4606H-101-102LF]	1 kOhm [4608X-AP1-102LF]
1 kOhm [4310M-101-102LF]	1 kOhm [4416P-T02-102]	1 kOhm [4606H-102-102LF]	1 kOhm [4608X-AP2-102LF]
1 kOhm [4310M-102-102]	1 kOhm [4416P-T02-102LF]	1 kOhm [4606M-101-102LF]	1 kOhm [4609H-101-102LF]
1 kOhm [4310M-102-102LF]	1 kOhm [4420P-1-102]	1 kOhm [4606M-102-102LF]	1 kOhm [4609M-101-102LF]
1 kOhm [4310R-101-102]	1 kOhm [4420P-2-102]	1 kOhm [4606X-101-102LF]	1 kOhm [4609X-101-102LF]
1 kOhm [4310R-101-102LF]	1 kOhm [4420P-2-102LF]	1 kOhm [4606X-102-102LF]	1 kOhm [4609X-AP1-102LF]

Multisim 14.1 Education Components

1 kOhm [4610H-101-102LF]	1 kOhm [4814P-1-102LF]	1 kOhm [4816P-T01-102LF]	1 kOhm [CAT10-102J4LF]
1 kOhm [4610H-102-102LF]	1 kOhm [4814P-2-102]	1 kOhm [4816P-T02-102]	1 kOhm [CAT16-1001F4LF]
1 kOhm [4610M-101-102LF]	1 kOhm [4814P-2-102LF]	1 kOhm [4816P-T02-102LF]	1 kOhm [CAT16-1001F8LF]
1 kOhm [4610M-102-102LF]	1 kOhm [4814P-T01-102]	1 kOhm [4818P-1-102]	1 kOhm [CAT16-102J2LF]
1 kOhm [4610X-101-102LF]	1 kOhm [4814P-T01-102LF]	1 kOhm [4818P-2-102]	1 kOhm [CAT16-102J4GLF]
1 kOhm [4610X-102-102LF]	1 kOhm [4814P-T02-102]	1 kOhm [4818P-T01-102]	1 kOhm [CAT16-102J4LF]
1 kOhm [4610X-AP1-102LF]	1 kOhm [4814P-T02-102LF]	1 kOhm [4818P-T02-102]	1 kOhm [CAT16-102J8LF]
1 kOhm [4610X-AP2-102LF]	1 kOhm [4816P-1-102]	1 kOhm [4820P-1-102]	1 kOhm [CAT25-102JALF]
1 kOhm [4611M-101-102LF]	1 kOhm [4816P-1-102F]	1 kOhm [4820P-1-102LF]	1 kOhm [CAY10-102J4LF]
1 kOhm [4611X-101-102LF]	1 kOhm [4816P-1-102LF]	1 kOhm [4820P-2-102]	1 kOhm [CAY16-1001F4LF]
1 kOhm [4612X-101-102LF]	1 kOhm [4816P-2-102]	1 kOhm [4820P-2-102LF]	1 kOhm [CAY16-102J2LF]
1 kOhm [4612X-102-102LF]	1 kOhm [4816P-2-102F]	1 kOhm [4820P-T01-102]	1 kOhm [CAY16-102J4GLF]
1 kOhm [4613X-101-102LF]	1 kOhm [4816P-2-102LF]	1 kOhm [4820P-T01-102LF]	1 kOhm [CAY16-102J4LF]
1 kOhm [4614X-102-102LF]	1 kOhm [4816P-4-102]	1 kOhm [4820P-T02-102]	1 kOhm [CAY16-102J8LF]
1 kOhm [4814P-1-102]	1 kOhm [4816P-T01-102]	1 kOhm [4820P-T02-102LF]	1 kOhm [CAY17-102JALF]

Multisim 14.1 Education Components

1 kOhm [CR0201-FW-1001GLF]	1 kOhm [CR1206-JW-102GLF]	1 kOhm [CRS2512-FX-1001ELF]	1 kOhm [CRT0805-FV-1001ELF]
1 kOhm [CR0201-JW-102GLF]	1 kOhm [CR2010-JW-102ELF]	1 kOhm [CRS2512-JX-102ELF]	1 kOhm [CRT1206-AV-1001ELF]
1 kOhm [CR0402-FX-1001GLF]	1 kOhm [CR2512-FX-1001ELF]	1 kOhm [CRT0402-BY-1001GLF]	1 kOhm [CRT1206-BW-1001ELF]
1 kOhm [CR0402-JW-102GLF]	1 kOhm [CR2512-JW-102ELF]	1 kOhm [CRT0402-DY-1001GLF]	1 kOhm [CRT1206-BY-1001ELF]
1 kOhm [CR0603-FX-1001ELF]	1 kOhm [CRM1206-FX-1001ELF]	1 kOhm [CRT0402-FZ-1001GLF]	1 kOhm [CRT1206-FZ-1001ELF]
1 kOhm [CR0603-FX-1001GLF]	1 kOhm [CRM1206-JW-102ELF]	1 kOhm [CRT0603-BY-1001EAS]	1 kOhm [PWR163S-25-1001F]
1 kOhm [CR0603-FX-1001HLF]	1 kOhm [CRM2010-FX-1001ELF]	1 kOhm [CRT0603-BY-1001ELF]	1 kOhm [PWR163S-25-1001J]
1 kOhm [CR0603-JW-102ELF]	1 kOhm [CRM2512-FX-1001ELF]	1 kOhm [CRT0603-DZ-1001ELF]	1 kOhm [PWR2010W1001FE]
1 kOhm [CR0603-JW-102GLF]	1 kOhm [CRM2512-FX-1001ELF]	1 kOhm [CRT0603-FY-1001ELF]	1 kOhm [PWR220T-20-1001F]
1 kOhm [CR0805-FX-1001ELF]	1 kOhm [CRM2512-JW-102ELF]	1 kOhm [CRT0603-PW-1001ELF]	1 kOhm [PWR220T-20-1001J]
1 kOhm [CR0805-JW-102ELF]	1 kOhm [CRS0805-FX-1001ELF]	1 kOhm [CRT0805-BV-1001ELF]	1 kOhm [PWR220T-35-1001F]
1 kOhm [CR0805-JW-102GLF]	1 kOhm [CRS0805-JX-102ELF]	1 kOhm [CRT0805-BW-1001ELF]	1 kOhm [PWR220T-35-1001J]
1 kOhm [CR1206-FX-1001ELF]	1 kOhm [CRS1206-FX-1001ELF]	1 kOhm [CRT0805-BY-1001ELF]	1 kOhm [PWR221T-30-1001F]
1 kOhm [CR1206-FX-1001GLF]	1 kOhm [CRS2010-FX-1001ELF]	1 kOhm [CRT0805-DV-1001ELF]	
1 kOhm [CR1206-JW-102ELF]		1 kOhm [CRT0805-DY-1001ELF]	

Multisim 14.1 Education Components

1 kOhm [PWR221T-50-1001J]	1 kOhm [PWR6327W1001JE]	1 mF [T510E108M004AT E010]	1 mF [T520X108M2R5AT E010]
1 kOhm [PWR2615W1001F]	1 kOhm [WS2M1001J]	1 mF [T510E108M004AT E018]	1 mF [T520Y108M2R5AT E010]
1 kOhm [PWR263S-20-1001F]	1 kOhm [WS5M1001J]	1 mF [T510X108M004AT E018]	1 mF [T520Y108M2R5AT E015]
1 kOhm [PWR263S-20-1001FE]	1 mF [2R5TPE1000MF]		
1 kOhm [PWR263S-20-1001J]	1 mF [2SEPC1000MX]	1 mF [T510X108M004AT E023]	1 mF [T520Y108M2R5AT E025]
1 kOhm [PWR263S-35-1001F]	1 mF [ETPF1000M5H]	1 mF [T513E108M004AH 6110]	1 mF [T530X108M003AT E010]
1 kOhm [PWR263S-35-1001FE]	1 mF [ETPF1000M6H]	1 mF [T513X108M004AH 6110]	1 mF [T530X108M004AT E006]
1 kOhm [PWR263S-35-1001J]	1 mF [T491E108M004AT]		
1 kOhm [PWR4318W1001FE]	1 mF [T491X108M004AT]	1 mF [T513X108M004AH 6120]	1 mF [T530X108M2R5AT E005]
1 kOhm [PWR4318W1001JE]	1 mF [T494E108M004AT]	1 mF [T520D108M2R5AT E015]	1 mF [T530X108M2R5AT E006]
1 kOhm [PWR4525W1001J]	1 mF [T495E108M004AT E035]	1 mF [T520D108M2R5AT E030]	1 mF [T530Y108M2R5AT E005]
1 kOhm [PWR4525W1001JE]	1 mF [T495E108M006AT E050]	1 mF [T520X108M003AT E015]	1 mF [TAJD108K004RNJ]
1 kOhm [PWR6327W1001J]	1 mF [T495X108M004AT E070]	1 mF [T520X108M003AT E030]	1 mF [TAJE108K002RNJ]
			1 mF [TAJE108K004RNJ]

Multisim 14.1 Education Components

1 mF [TAJV108K004RNJ]	1 mF [TPSV108K004R003 5]	1 mH [SDR1005- 102KL]	1 mH [SRR0906- 102YL]
1 mF [TAJV108K006RNJ]	1 mF [TPSV108K004R004 0]	1 mH [SDR1006- 102KL]	1 mH [SRR0908- 102YL]
1 mF [TPMD108K004R00 25]	1 mF [TPSV108K004R005 0]	1 mH [SDR1030- 102K]	1 mH [SRR1005- 102K]
1 mF [TPMD108K004R00 45]	1 mF [TPSV108K006R004 0]	1 mH [SDR1045- 102K]	1 mH [SRR1206- 102KL]
1 mF [TPME108K004R00 18]	1 mF [TPSV108K006R005 0]	1 mH [SDR1305- 102K]	1 mH [SRR1208- 102KL]
1 mF [TPME108K004R00 23]	1 mF [TRME108K004R00 23]	1 mH [SDR1307- 102KL]	1 mH [SRR1210- 102M]
1 mF [TPME108K004R00 23]	1 mF [TRME108K004R00 23]	1 mH [SDR1307A- 102K]	1 mH [SRR1210A- 102M]
1 mF [TPMV108K004R00 18]	1 mH [SDR0302- 102KL]	1 mH [SDR1806- 102KL]	1 mH [SRR1240- 102K]
1 mF [TPSE108K002R003 0]	1 mH [SDR0403- 102KL]	1 mH [SDR6603- 102M]	1 mH [SRR1260- 102K]
1 mF [TPSE108K002R004 0]	1 mH [SDR0503- 102KL]	1 mH [SDR7030- 102K]	1 mH [SRR1260A- 102K]
1 mF [TPSE108K004R004 0]	1 mH [SDR0604- 102KL]	1 mH [SDR7045- 102K]	1 mH [SRR1280- 102K]
1 mF [TPSE108K004R004 0]	1 mH [SDR0703- 102KL]	1 mH [SRR0603- 102KL]	1 mH [SRR1806- 102M]
1 mF [TPSE108K004R006 0]	1 mH [SDR0805- 102KL]	1 mH [SRR0604- 102KL]	1 mH [SRR6028- 102Y]
1 mF [TPSV108K004R002 5]	1 mH [SDR0906- 102KL]	1 mH [SRR0745A- 102M]	1 mH [SRR6603- 102ML]
		1 mH [SRR0805- 102K]	1 mH [SRR7032- 102M]

Multisim 14.1 Education Components

1 mH [SRR7045-102M]	1 MOhm [4306R-102-105LF]	1 MOhm [4310R-102-105]	1 MOhm [4606X-AP2-105LF]
1 MOhm [4114R-1-105]	1 MOhm [4308H-101-105]	1 MOhm [4310R-102-105LF]	1 MOhm [4607M-101-105LF]
1 MOhm [4114R-1-105LF]	1 MOhm [4308M-102-105]	1 MOhm [4311R-101-105LF]	1 MOhm [4607X-101-105LF]
1 MOhm [4114R-2-105]	1 MOhm [4308R-101-105]	1 MOhm [4416P-1-105]	1 MOhm [4608X-101-105LF]
1 MOhm [4114R-2-105LF]	1 MOhm [4308R-101-105LF]	1 MOhm [4416P-2-105]	1 MOhm [4608X-102-105LF]
1 MOhm [4116R-1-105]	1 MOhm [4308R-102-105]	1 MOhm [4416P-T01-105]	1 MOhm [4608X-AP1-105LF]
1 MOhm [4116R-1-105LF]	1 MOhm [4308R-102-105LF]	1 MOhm [4416P-T02-105]	1 MOhm [4608X-AP2-105LF]
1 MOhm [4116R-2-105]	1 MOhm [4309R-101-105]	1 MOhm [4420P-T01-105]	1 MOhm [4609M-101-105LF]
1 MOhm [4116R-2-105LF]	1 MOhm [4309R-101-105LF]	1 MOhm [4604X-101-105LF]	1 MOhm [4609X-101-105LF]
1 MOhm [4306H-101-105]	1 MOhm [4310H-102-105]	1 MOhm [4604X-102-105LF]	1 MOhm [4610X-101-105LF]
1 MOhm [4306H-101-105LF]	1 MOhm [4310H-102-105LF]	1 MOhm [4605X-101-105LF]	1 MOhm [4610X-102-105LF]
1 MOhm [4306M-102-105]	1 MOhm [4310M-102-105]	1 MOhm [4605X-AP1-105LF]	1 MOhm [4610X-AP2-105LF]
1 MOhm [4306R-101-105]	1 MOhm [4310M-102-105LF]	1 MOhm [4606M-102-105LF]	1 MOhm [4611X-101-105LF]
1 MOhm [4306R-101-105LF]	1 MOhm [4310R-101-105]	1 MOhm [4606X-101-105LF]	1 MOhm [4612X-102-105LF]
1 MOhm [4306R-102-105]	1 MOhm [4310R-101-105LF]	1 MOhm [4606X-102-105LF]	1 MOhm [4614X-102-105LF]

Multisim 14.1 Education Components

1 MOhm [4814P-1-105]	1 MOhm [4818P-2-105]	1 MOhm [CAY16-105J4GLF]	1 MOhm [CR0201-FW-1004GLF]
1 MOhm [4814P-1-105LF]	1 MOhm [4820P-1-105]	1 MOhm [CAY16-105J4LF]	1 MOhm [CR0402-FX-1004GLF]
1 MOhm [4814P-2-105]	1 MOhm [4820P-2-105]	1 MOhm [CAY16-105J8LF]	1 MOhm [CR0402-JW-105GLF]
1 MOhm [4814P-2-105LF]	1 MOhm [4820P-2-105F]	1 MOhm [CHV0603-JW-105ELF]	1 MOhm [CR0603-FX-1004ELF]
1 MOhm [4814P-T01-105]	1 MOhm [4820P-T01-105]	1 MOhm [CHV0805-FX-1004ELF]	1 MOhm [CR0603-JW-105ELF]
1 MOhm [4814P-T01-105LF]	1 MOhm [4820P-T02-105]	1 MOhm [CHV0805-JW-105ELF]	1 MOhm [CR0603-JW-105GLF]
1 MOhm [4814P-T02-105]	1 MOhm [CAT10-105J4LF]	1 MOhm [CHV1206-FW-1004ELF]	1 MOhm [CR0805-FX-1004ELF]
1 MOhm [4816P-1-105]	1 MOhm [CAT16-1004F4LF]	1 MOhm [CHV1206-FX-1004ELF]	1 MOhm [CR0805-JW-105ELF]
1 MOhm [4816P-1-105LF]	1 MOhm [CAT16-105J2LF]	1 MOhm [CHV1206-JW-105ELF]	1 MOhm [CR1206-FX-1004ELF]
1 MOhm [4816P-2-105]	1 MOhm [CAT16-105J4LF]	1 MOhm [CHV2010-FW-1004ELF]	1 MOhm [CR1206-JW-105ELF]
1 MOhm [4816P-2-105LF]	1 MOhm [CAT16-105J8LF]	1 MOhm [CHV2512-FX-1004ELF]	1 MOhm [CR1206-JW-105GLF]
1 MOhm [4816P-T01-105]	1 MOhm [CAT25-105JALF]	1 MOhm [CHV2512-JW-105ELF]	1 mOhm [CRE2512-FZ-R001E-2]
1 MOhm [4816P-T01-105LF]	1 MOhm [CAY10-105J4LF]	1 MOhm [CHV2512-JW-105ELF]	1 mOhm [CRE2512-FZ-R001E-3]
1 MOhm [4816P-T02-105]	1 MOhm [CAY16-1004F4LF]	1 MOhm [CHV2512-JW-105ELF]	1 mOhm [CRF2512-FV-R001ELF]
1 MOhm [4816P-T02-105LF]	1 MOhm [CAY16-105J2LF]		1 mOhm [CRF2512-JV-R001ELF]

Multisim 14.1 Education Components

1 MOhm [CRM1206-FX-1004ELF]	1 MOhm [CRT0805-DY-1004ELF]	1 nF [C0402C102K1HACTU]	1 nF [C0603C102K2RACTU]
1 MOhm [CRM1206-JW-105ELF]	1 MOhm [CRT1206-BW-1004ELF]	1 nF [C0402C102K3GACTU]	1 nF [C0603C102K3GACTU]
1 MOhm [CRM2512-FX-1004ELF]	1 MOhm [CRT1206-BY-1004ELF]	1 nF [C0402C102K3HACTU]	1 nF [C0603C102K3HACTU]
1 MOhm [CRM2512-JW-105ELF]	1 MOhm [CRT1206-DY-1004ELF]	1 nF [C0402C102K3RACTU]	1 nF [C0603C102K3RACTU]
1 MOhm [CRS0805-FX-1004ELF]	1 MOhm [CRT1206-FZ-1004ELF]	1 nF [C0402C102K4RACTU]	1 nF [C0603C102K4GACTU]
1 MOhm [CRS1206-FX-1004ELF]	1 mOhm [CST0612-FC-R001E]	1 nF [C0402C102K5HACTU]	1 nF [C0603C102K4RACTU]
1 MOhm [CRS2010-FX-1004ELF]	1 nF [03063C102KAT2A]	1 nF [C0402C102K5RACTU]	1 nF [C0603C102K5GACTU]
1 MOhm [CRS2512-FX-1004ELF]	1 nF [03066C102KAT2A]	1 nF [C0402C102K8RACTU]	1 nF [C0603C102K5HACTU]
1 MOhm [CRT0603-BZ-1004ELF]	1 nF [0306ZC102KAT2A]	1 nF [C0402C102K9RACTU]	1 nF [C0603C102K5RACTU]
1 MOhm [CRT0603-DZ-1004ELF]	1 nF [05083C102KAT2S]	1 nF [C0603C102K1HACTU]	1 nF [C0603C102K8RACTU]
1 MOhm [CRT0805-BY-1004ELF]	1 nF [06123C102KAT2S]	1 nF [C0603C102K1RACTU]	1 nF [C0603C102K9RACTU]

Multisim 14.1 Education Components

1 nF [C0805C102K1GACT U]	1 nF [C1206C102K1RACT U]	1 nF [C1210C102KBGAC TU]	1 nF [C2225C102KBGAC TU]
1 nF [C0805C102K1RACT U]	1 nF [C1206C102K2GACT U]	1 nF [C1210C102KCGAC TU]	1 nF [CA064C102K3RACT U]
1 nF [C0805C102K2RACT U]	1 nF [C1206C102K2RACT U]	1 nF [C1210C102KDGAC TU]	1 nF [CA064C102K4RACT U]
1 nF [C0805C102K3GACT U]	1 nF [C1206C102K3RACT U]	1 nF [C1812C102K1GACT U]	1 nF [CA064C102K5RACT U]
1 nF [C0805C102K3RACT U]	1 nF [C1206C102K4RACT U]	1 nF [C1812C102K2GACT U]	1 nF [CA064C102K8RACT U]
1 nF [C0805C102K4RACT U]	1 nF [C1206C102K5GACT U]	1 nF [C1812C102K5GACT U]	1 nF [GMC5.7102K100J3 1TR12]
1 nF [C0805C102K5GACT U]	1 nF [C1206C102K5RACT U]	1 nF [C1812C102KBGAC TU]	1 nF [GMC5.7102K50J31 TR12]
1 nF [C0805C102K5RACT U]	1 nF [C1206C102KCGAC TU]	1 nF [C1812C102KCGAC TU]	1 nF [GMC5.7103K250J3 1TR12]
1 nF [C0805C102K8RACT U]	1 nF [C1210C102K1GACT U]	1 nF [C1812C102KDGAC TU]	1 nF [GMC7.3102K100K3 1TR12]
1 nF [C0805C102KARACT U]	1 nF [C1210C102K2GACT U]	1 nF [C1825C102KBGAC TU]	1 nF [GMC7.3102K63K31 TR12]
1 nF [C1206C102K1GACT U]	1 nF [C1210C102K5GACT U]	1 nF [C2220C102KBGAC TU]	1 nF [GMC7.3103K250K3 1TR12]

Multisim 14.1 Education Components

1 nF [GMC7.3103K63K31 TR12]	1 nF [MMC7.3102K100K 31TR12]	1 Ohm [CR0805-J/- 1R0ELF]	1 Ohm [CRM2010- JW-1R0ELF]
1 nF [GPC7.3102K160K3 1TR12]	1 nF [MMC7.3102K250K 31TR12]	1 Ohm [CR1206-J/- 1R0ELF]	1 Ohm [CRM2512- FX-1R00ELF]
1 nF [GPC7.3102K630K3 1TR12]	1 nF [MMC7.3102K400K 31TR12]	1 Ohm [CR1206-J/- 1R0GLF]	1 Ohm [CRM2512- JW-1R0ELF]
1 nF [GPC7.3102K63K31 TR12]	1 nF [MMC7.3102K50K3 1TR12]	1 Ohm [CR2010-J/- 1R0ELF]	1 Ohm [CRS0805- FW-1R00ELF]
1 nF [LD163C102KAB2A]	1 nF [MMC7.3102K63K3 1TR12]	1 Ohm [CR2512-J/- 1R0ELF]	1 Ohm [CRS1206- FW-1R00ELF]
1 nF [LD16YC102KAB2A]	1 nF [MMC7.3102K63K3 1TR12]	1 Ohm [CRL0603- FW-1R00ELF]	1 Ohm [CRS2512- FW-1R00ELF]
1 nF [LD173C102KAB2S]	1 nF [SPC7.3102K100K31 TR12]	1 Ohm [CRL0805- FW-1R00ELF]	1 Ohm [CRT0805- CY-1R00ELF]
1 nF [LD175C102KAB2V]	1 nF [SPC7.3102K250K31 TR12]	1 Ohm [CRL1206- FW-1R00ELF]	1 Ohm [CRT0805- DY-1R00ELF]
1 nF [LD17YC102KAB2S]	1 nF [SPC7.3102K400K31 TR12]	1 Ohm [CRL2010- FW-1R00ELF]	1 Ohm [CRT0805- FY-1R00ELF]
1 nF [MMC5.7102K100J 31TR12]	1 nF [SPC7.3102K630K31 TR12]	1 Ohm [CRL2010- JW-1R00ELF]	1 Ohm [PWR163S- 25-1R00F]
1 nF [MMC5.7102K250J 31TR12]	1 nF [W2F15C1028AT1A]	1 Ohm [CRL2512- FW-1R00ELF]	1 Ohm [PWR163S- 25-1R00FE]
1 nF [MMC5.7102K50J3 1TR12]	1 Ohm [CR0402-J/- 1R0GLF]	1 Ohm [CRL2512- JW-1R00ELF]	1 Ohm [PWR163S- 25-1R00J]
	1 Ohm [CR0603-J/- 1R0ELF]	1 Ohm [CRM0805- JW-1R0ELF]	1 Ohm [PWR163S- 25-1R00JE]
		1 Ohm [CRM1206- FX-1R00ELF]	1 Ohm [PWR1913W1R00J]
		1 Ohm [CRM1206- JW-1R0ELF]	1 Ohm [PWR2010W1R00JE]

Multisim 14.1 Education Components

1 Ohm [PWR220T-20-1R00F]	1 Ohm [PWR4318W1R00JE]	1 uF [C0603C105K4PACT U]	1 uF [C0805C105K8RACT U]
1 Ohm [PWR220T-20-1R00J]	1 Ohm [PWR4525W1R00JE]	1 uF [C0603C105K4RACT U]	1 uF [C0805C105K9PACT U]
1 Ohm [PWR220T-35-1R00F]	1 Ohm [PWR5322W1R00JE]	1 uF [C0603C105K8PACT U]	1 uF [C0805C105K9RACT U]
1 Ohm [PWR221T-30-1R00F]	1 Ohm [PWR6327W1R00F]	1 uF [C0603C105K8RACT U]	1 uF [C0805C105M3VAC TU]
1 Ohm [PWR221T-30-1R00J]	1 Ohm [PWR6327W1R00JE]	1 uF [C0603C105K9PACT U]	1 uF [C0805C105M4VAC TU]
1 Ohm [PWR2615N1R00F]	1 uF [05086C105KAT2A]	1 uF [C0603C105K9RACT U]	1 uF [C0805C105M8VAC TU]
1 Ohm [PWR2615W1R00F]	1 uF [0508ZC105KAT2A]	1 uF [C0805C105K3PACT U]	1 uF [C1206C105K3NAC TU]
1 Ohm [PWR2615W1R00J]	1 uF [06126C105KAT2V]	1 uF [C0805C105K4PACT U]	1 uF [C1206C105K3PACT U]
1 Ohm [PWR263S-20-1R00F]	1 uF [0612YC105KAT2A]	1 uF [C0805C105K4PACT U]	1 uF [C1206C105K3PACT U]
1 Ohm [PWR263S-20-1R00J]	1 uF [0612ZC105KAT2V]	1 uF [C0805C105K4PACT U]	1 uF [C1206C105K3PACT U]
1 Ohm [PWR263S-35-1R00F]	1 uF [C0402C105K8PACT U]	1 uF [C0805C105K8NAC TU]	1 uF [C1206C105K4PACT U]
1 Ohm [PWR263S-35-1R00FE]	1 uF [C0402C105K9PACT U]	1 uF [C0805C105K8PACT U]	1 uF [C1206C105K5PACT U]
1 Ohm [PWR263S-35-1R00J]	1 uF [C0603C105K3PACT U]		
1 Ohm [PWR3014W1R00JE]			

Multisim 14.1 Education Components

1 uF [C1206C105K8RACT U]	1 uF [C1210C105K5NAC TU]	1 uF [C1812C105K5RACT U]	1 uF [C2220C105KARACT U]
1 uF [C1206C105K9RACT U]	1 uF [C1210C105K5PACT U]	1 uF [C1812C105M5UAC TU]	1 uF [C2225C105K1RACT U]
1 uF [C1206C105M3VAC TU]	1 uF [C1210C105K5RACT U]	1 uF [C1812F105K1RACT U]	1 uF [C2225C105K5RACT U]
1 uF [C1206C105M4VAC TU]	1 uF [C1210C105K8RACT U]	1 uF [C1812F105K3RACT U]	1 uF [C2225C105KARACT U]
1 uF [C1206C105M8VAC TU]	1 uF [C1210C105K9RACT U]	1 uF [C1812F105K5RACT U]	1 uF [C2225C105M5UAC TU]
1 uF [C1206F105K4RACT U]	1 uF [C1210C105M3VAC TU]	1 uF [C1825C105K2RACT U]	1 uF [LD17ZC105KAB2A]
1 uF [C1210C105K1RACT U]	1 uF [C1210C105M5UAC TU]	1 uF [C1825C105K5RACT U]	1 uF [LD18YC105KAB2A]
1 uF [C1210C105K3PACT U]	1 uF [C1210C105M8VAC TU]	1 uF [C1825C105KARACT U]	1 uF [LD18ZC105KAB2V]
1 uF [C1210C105K3RACT U]	1 uF [C1210F105K3RACT U]	1 uF [C1825C105M5UAC TU]	1 uF [MDC10105K100A5 2P3TUBE]
1 uF [C1210C105K4PACT U]	1 uF [C1210F105K4RACT U]	1 uF [C2220C105K5R1C7 186]	1 uF [MDC10105K250A5 7P7TUBE]
1 uF [C1210C105K4RACT U]	1 uF [C1812C105K3RACT U]	1 uF [C2220C105K5RACT U]	1 uF [MDC10105K250A5 7P8TUBE]

Multisim 14.1 Education Components

1 uF [MDC10105K50A52 P3TUBE]	1 uF [T491A105M025AT]	1 uF [T494C105M050AT]	1 uF [TAJA105K016RNJ]
1 uF [MDC15105K100B5 3P3TUBE]	1 uF [T491A105M035AT]	1 uF [T494S105M020AT]	1 uF [TAJA105K020RNJ]
1 uF [MDC15105K50B53 P3TUBE]	1 uF [T491B105M025AT]	1 uF [T494V105M050AT]	1 uF [TAJA105K025RNJ]
1 uF [MDK10105K50A52 P3TUBE]	1 uF [T491B105M035AT]	1 uF [T495A105M020AT E3K0]	1 uF [TAJA105K035RNJ]
1 uF [MDK10105K50A52 P3TUBE]	1 uF [T491B105M050AT]	1 uF [T495A105M035AT E3K0]	1 uF [TAJB105K035RNJ]
1 uF [MDS10105K100A5 2P3TUBE]	1 uF [T491C105M050AT]	1 uF [T495A105M035AT E3K0]	1 uF [TAJB105K050RNJ]
1 uF [MDS10105K50A52 P3TUBE]	1 uF [T491S105M020AT]	1 uF [T495B105M035AT E1K7]	1 uF [TAJC105K050RNJ]
1 uF [MDS10105K50A52 P3TUBE]	1 uF [T491V105M050AT]	1 uF [T497A105M015AT 6110]	1 uF [TAJP105K025RNJ]
1 uF [MDS15105K100B5 3P3TUBE]	1 uF [T494A105M016AT]	1 uF [T497A105M015AT 6110]	1 uF [TAJP105K035RNJ]
1 uF [PGC26D105MAB2S 1]	1 uF [T494A105M020AT]	1 uF [T498A105M016AT E6K5]	1 uF [TAJR105K010RNJ]
1 uF [T409C105M025AH 4250]	1 uF [T494A105M025AT]	1 uF [T498A105M020AT E5K9]	1 uF [TAJR105K016RNJ]
1 uF [T489A105M025AT E6K6]	1 uF [T494A105M035AT]	1 uF [T498A105M035AT E10K]	1 uF [TAJR105K020RNJ]
1 uF [T491A105M016AT]	1 uF [T494B105M025AT]	1 uF [T498A105M035AT E10K]	1 uF [TAJR105K025RNJ]
1 uF [T491A105M020AT]	1 uF [T494B105M035AT]	1 uF [TACL105K006RTA]	1 uF [TAJS105K010RNJ]
	1 uF [T494B105M050AT]	1 uF [TACL105K010RTA]	1 uF [TAJS105K016RNJ]
		1 uF [TACL105K016RTA]	

Multisim 14.1 Education Components

1 uF [TAJS105K020RNJ]	1 uF [TPSB105K050R300 0]	1 uH [SDR0302- 1R0ML]	1 uH [SRN4026- 1R0Y]
1 uF [TAJS105K025RNJ]	1 uF [TPSC105K050R250 0]	1 uH [SDR0403- 1R0ML]	1 uH [SRN5020- 1R0Y]
1 uF [TAJS105K035RNJ]	1 uF [TPSR105K010R900 0]	1 uH [SDR0703- 1R0ML]	1 uH [SRN6045- 1R0Y]
1 uF [TAJT105K016RNJ]	1 uF [TPSR105K020R600 0]	1 uH [SDR1806- 1R0ML]	1 uH [SRP1038A- 1R0M]
1 uF [TAJT105K020RNJ]	1 uF [TPSS105K020R600 0]	1 uH [SDR6603- 1R0M]	1 uH [SRP1040- 1R0M]
1 uF [TAJT105K035RNJ]	1 uF [TPST105K020R200 0]	1 uH [SDR7030- 1R0M]	1 uH [SRP1235- 1R0M]
1 uF [TAJW105K050RNJ]	1 uF [TRJA105K020RRJ]	1 uH [SRN2010- 1R0M]	1 uH [SRP1245A- 1R0M]
1 uF [THJA105K025RJN]	1 uF [TRJA105K025RRJ]	1 uH [SRN2012- 1R0M]	1 uH [SRP1250- 1R0M]
1 uF [THJA105K035RJN]	1 uF [TRJA105K035RRJ]	1 uH [SRN2510- 1R0M]	1 uH [SRP1265A- 1R0M]
1 uF [THJB105K035RJN]	1 uF [TRJB105K035RRJ]	1 uH [SRN2512- 1R0M]	1 uH [SRP1270- 1R0M]
1 uF [TPSA105K020R300 0]	1 uF [TRJC105K050RRJ]	1 uH [SRN3010- 1R0Y]	1 uH [SRP1770TA- 1R0M]
1 uF [TPSA105K025R400 0]	1 uF [W3L16C105MAT1 A]	1 uH [SRN3015- 1R0Y]	1 uH [SRP4012- 1R0M]
1 uF [TPSA105K035R300 0]	1 uH [SDE0403A- 1R0M]	1 uH [SRN4012T- 1R0M]	1 uH [SRP4012TA- 1R0M]
1 uF [TPSB105K035R200 0]		1 uH [SRN4018- 1R0Y]	1 uH [SRP4020- 1R0M]

Multisim 14.1 Education Components

1 uH [SRP4020TA-1ROM]	1 uH [SRR6040A-1ROY]	1.02 kOhm [CR1206-FX-1021ELF]	1.07 kOhm [CR0805-FX-1071ELF]
1 uH [SRP5015TA-1ROM]	1 uH [SRR6603-1ROML]	1.02 kOhm [CRT1206-BY-1021ELF]	1.07 kOhm [CR1206-FX-1071ELF]
1 uH [SRP5030T-1ROM]	1 uH [SRR7045-1ROM]	1.02 MOhm [CR1206-FW-1024ELF]	1.07 kOhm [CR2010-FX-1071ELF]
1 uH [SRP5030TA-1ROM]	1 uH [SRU1028-1ROY]	1.05 kOhm [CR0402-FX-1051GLF]	1.07 MOhm [CR1206-FW-1074ELF]
1 uH [SRP6540-1ROM]	1 uH [SRU1028A-1ROY]	1.05 kOhm [CR0603-FX-1051ELF]	1.1 kOhm [4310R-101-112]
1 uH [SRP7028A-1ROM]	1 uH [SRU2009-1ROY]	1.05 kOhm [CR0603-FX-1051ELF]	1.1 kOhm [4605X-101-112LF]
1 uH [SRP7030-1ROFM]	1 uH [SRU2011-1ROY]	1.05 kOhm [CR0805-FX-1051ELF]	1.1 kOhm [CAT16-1101F4LF]
1 uH [SRP7050TA-1ROM]	1 uH [SRU2013-1ROY]	1.05 kOhm [CR1206-FX-1051ELF]	1.1 kOhm [CAT16-112J4LF]
1 uH [SRR1005-1ROM]	1 uH [SRU2016-1ROY]	1.05 kOhm [CRT0603-BY-1051ELF]	1.1 kOhm [CR0402-FX-1101GLF]
1 uH [SRR1210-1ROY]	1 uH [SRU5018-1ROY]	1.05 kOhm [CRT0805-BY-1051ELF]	1.1 kOhm [CR0603-FX-1101ELF]
1 uH [SRR1210A-1ROY]	1 uH [SRU8028-1ROY]	1.07 kOhm [CR0402-FX-1071GLF]	1.1 kOhm [CR0603-JW-112ELF]
1 uH [SRR1240-1ROY]	1.02 kOhm [CR0402-FX-1021GLF]	1.07 kOhm [CR0805-FX-1101ELF]	1.1 kOhm [CR0805-FX-1101ELF]
1 uH [SRR1260-1ROY]	1.02 kOhm [CR0603-FX-1021ELF]	1.07 kOhm [CR0805-FX-1101ELF]	1.1 kOhm [CR0805-FX-1101ELF]
1 uH [SRR1260A-1ROY]	1.02 kOhm [CR0805-FX-1021ELF]		
1 uH [SRR4018-1ROY]			

Multisim 14.1 Education Components

1.1 kOhm [CR1206-FX-1101ELF]	1.1 MOhm [CR1206-FW-1104ELF]	1.1 nF [C2225C112KBGAC TU]	1.1 uH [SRP7030-1R1FM]
1.1 kOhm [CR1206-JW-112ELF]	1.1 MOhm [CR1206-JW-115ELF]	1.1 nF [CDR33BP112BKSM]	1.1 uH [SRR1280-1R1Y]
1.1 kOhm [CR2512-JW-112ELF]	1.1 nF [C0402C112K3HACT U]	1.1 Ohm [CR0805-J/-1R1ELF]	1.13 kOhm [CR0201-FW-1131GLF]
1.1 kOhm [CRT0402-FZ-1101GLF]	1.1 nF [C0402C112K5HACT U]	1.1 Ohm [CR1206-J/-1R1ELF]	1.13 kOhm [CR0402-FX-1131GLF]
1.1 kOhm [CRT0603-BY-1101ELF]	1.1 nF [C0603C112K1HACT U]	1.1 Ohm [CRL0603-FW-1R10ELF]	1.13 kOhm [CR0603-FX-1131ELF]
1.1 kOhm [CRT0805-BY-1101ELF]	1.1 nF [C0603C112K3HACT U]	1.1 Ohm [CRL0805-FW-1R10ELF]	1.13 kOhm [CR0805-FX-1131ELF]
1.1 kOhm [CRT0805-DY-1101ELF]	1.1 nF [C0603C112K5HACT U]	1.1 Ohm [CRL1206-FW-1R10ELF]	1.13 kOhm [CRM2512-FX-1131ELF]
1.1 kOhm [CRT0805-FY-1101ELF]	1.1 nF [C1210C112KBGAC TU]	1.1 Ohm [CRL2010-FW-1R10ELF]	1.13 kOhm [CRT0805-BY-1131ELF]
1.1 MOhm [CR0402-FW-1104GLF]	1.1 nF [C1812C112KBGAC TU]	1.1 Ohm [CRL2010-FW-1R10ELF]	1.13 MOhm [CR1206-FW-1134ELF]
1.1 MOhm [CR0402-JW-115GLF]	1.1 nF [C1825C112KBGAC TU]	1.1 Ohm [CRL2512-FW-1R10ELF]	1.15 kOhm [CR0402-FX-1151GLF]
1.1 MOhm [CR0603-JW-115ELF]	1.1 nF [C2220C112KBGAC TU]	1.1 Ohm [PWR4318W1R10F]	1.15 kOhm [CR0603-FX-1151ELF]
1.1 MOhm [CR0805-JW-115ELF]			

Multisim 14.1 Education Components

1.15 kOhm [CR0805-FX- 1151ELF]	1.2 kOhm [4116R- 2-122LF]	1.2 kOhm [4308M- 102-122]	1.2 kOhm [4310R- 101-122]
1.15 kOhm [CR1206-FX- 1151ELF]	1.2 kOhm [4306H- 101-122]	1.2 kOhm [4308M- 102-122LF]	1.2 kOhm [4310R- 101-122LF]
1.18 kOhm [CR0402-FX- 1181GLF]	1.2 kOhm [4306H- 101-122LF]	1.2 kOhm [4308R- 101-122]	1.2 kOhm [4310R- 102-122]
1.18 kOhm [CR0603-FX- 1181ELF]	1.2 kOhm [4306M- 101-122]	1.2 kOhm [4308R- 101-122LF]	1.2 kOhm [4310R- 102-122LF]
1.18 kOhm [CR0603-FX- 1181ELF]	1.2 kOhm [4306M- 101-122LF]	1.2 kOhm [4308R- 102-122]	1.2 kOhm [4416P- 1-122]
1.18 kOhm [CR0805-FX- 1181ELF]	1.2 kOhm [4306M- 102-122]	1.2 kOhm [4308R- 102-122LF]	1.2 kOhm [4416P- 2-122]
1.18 kOhm [CR0805-FX- 1181ELF]	1.2 kOhm [4306M- 102-122LF]	1.2 kOhm [4309R- 101-122]	1.2 kOhm [4416P- T01-122]
1.18 kOhm [CR1206-FX- 1181ELF]	1.2 kOhm [4306R- 101-122]	1.2 kOhm [4309R- 101-122LF]	1.2 kOhm [4420P- 1-122]
1.2 kOhm [4114R- 1-122]	1.2 kOhm [4306R- 101-122LF]	1.2 kOhm [4310H- 101-122]	1.2 kOhm [4420P- T01-122]
1.2 kOhm [4114R- 1-122LF]	1.2 kOhm [4306R- 102-122]	1.2 kOhm [4310H- 101-122LF]	1.2 kOhm [4420P- T02-122]
1.2 kOhm [4114R- 2-122]	1.2 kOhm [4306R- 102-122LF]	1.2 kOhm [4310H- 102-122]	1.2 kOhm [4604X- 101-122LF]
1.2 kOhm [4114R- 2-122LF]	1.2 kOhm [4308H- 102-122]	1.2 kOhm [4310H- 102-122LF]	1.2 kOhm [4604X- 102-122LF]
1.2 kOhm [4116R- 1-122]	1.2 kOhm [4308H- 102-122LF]	1.2 kOhm [4310M- 101-122]	1.2 kOhm [4605M- 101-122LF]
1.2 kOhm [4116R- 1-122LF]	1.2 kOhm [4308M- 101-122]	1.2 kOhm [4310M- 102-122]	1.2 kOhm [4605X- 101-122LF]
1.2 kOhm [4116R- 2-122]	1.2 kOhm [4308M- 101-122LF]	1.2 kOhm [4310M- 102-122LF]	1.2 kOhm [4606H- 101-122LF]

Multisim 14.1 Education Components

1.2 kOhm [4606X-101-122LF]	1.2 kOhm [4611X-101-122LF]	1.2 kOhm [4818P-T02-122]	1.2 kOhm [CR0402-JW-122GLF]
1.2 kOhm [4606X-102-122LF]	1.2 kOhm [4612X-102-122LF]	1.2 kOhm [4820P-1-122]	1.2 kOhm [CR0603-FX-1201ELF]
1.2 kOhm [4606X-AP1-122LF]	1.2 kOhm [4614X-101-122LF]	1.2 kOhm [4820P-2-122]	1.2 kOhm [CR0603-JW-122ELF]
1.2 kOhm [4607X-101-122LF]	1.2 kOhm [4614X-102-122LF]	1.2 kOhm [4820P-2-122LF]	1.2 kOhm [CR0603-JW-122GLF]
1.2 kOhm [4608H-101-122LF]	1.2 kOhm [4814P-T01-122]	1.2 kOhm [4820P-T01-122]	1.2 kOhm [CR0805-FX-1201ELF]
1.2 kOhm [4608H-102-122LF]	1.2 kOhm [4814P-T02-122]	1.2 kOhm [CAT16-1201F4LF]	1.2 kOhm [CR0805-FX-1201GLF]
1.2 kOhm [4608X-101-122LF]	1.2 kOhm [4816P-1-122]	1.2 kOhm [CAT16-1201F8LF]	1.2 kOhm [CR0805-JW-122ELF]
1.2 kOhm [4608X-102-122LF]	1.2 kOhm [4816P-1-122LF]	1.2 kOhm [CAT16-122J4LF]	1.2 kOhm [CR1206-FX-1201ELF]
1.2 kOhm [4609H-101-122LF]	1.2 kOhm [4816P-2-122]	1.2 kOhm [CAT25-122JALF]	1.2 kOhm [CR1206-JW-122ELF]
1.2 kOhm [4609X-101-122LF]	1.2 kOhm [4816P-2-122LF]	1.2 kOhm [CAY10-122J4LF]	1.2 kOhm [CR2010-JW-122ELF]
1.2 kOhm [4610H-101-122LF]	1.2 kOhm [4816P-T01-122]	1.2 kOhm [CAY16-1201F4LF]	1.2 kOhm [CR2512-JW-122ELF]
1.2 kOhm [4610H-102-122LF]	1.2 kOhm [4816P-T01-122LF]	1.2 kOhm [CAY16-122J4LF]	1.2 kOhm [CRM1206-JW-122ELF]
1.2 kOhm [4610X-101-122LF]	1.2 kOhm [4816P-T02-122]	1.2 kOhm [CAY16-122J8LF]	1.2 kOhm [CRT0805-BY-1201ELF]
1.2 kOhm [4610X-102-122LF]	1.2 kOhm [4816P-T02-122LF]	1.2 kOhm [CAY17-122JALF]	1.2 kOhm [PWR163S-25-1201J]
1.2 kOhm [4610X-AP1-122LF]	1.2 kOhm [4818P-2-122]	1.2 kOhm [CR0402-FX-1201GLF]	

Multisim 14.1 Education Components

1.2 kOhm [PWR163S-25-1201JE]	1.2 MOhm [4608X-102-125LF]	1.2 nF [C0402C122K5RACTU]	1.2 nF [C0805C122K3GACTU]
1.2 kOhm [PWR263S-35-1201J]	1.2 MOhm [CAT25-125JALF]	1.2 nF [C0603C122K1HACTU]	1.2 nF [C0805C122K4RACTU]
1.2 kOhm [PWR263S-35-1201JE]	1.2 MOhm [CR0402-JW-125GLF]	1.2 nF [C0603C122K1RACTU]	1.2 nF [C0805C122K5GACTU]
1.2 mF [4SVPC1200M]	1.2 MOhm [CR0603-JW-125ELF]	1.2 nF [C0603C122K3HACTU]	1.2 nF [C0805C122K5RACTU]
1.2 mH [SDR0302-122KL]	1.2 MOhm [CR0805-FX-1204ELF]	1.2 nF [C0603C122K3RACTU]	1.2 nF [C0805C122KARACTU]
1.2 mH [SDR0503-122JL]	1.2 MOhm [CR0805-JW-125ELF]	1.2 nF [C0603C122K4RACTU]	1.2 nF [C1206C122K1GACTU]
1.2 mH [SDR0805-122KL]	1.2 MOhm [CR1206-FW-1204ELF]	1.2 nF [C0603C122K5HACTU]	1.2 nF [C1206C122K1RACTU]
1.2 mH [SDR0906-122KL]	1.2 MOhm [CR1206-JW-125ELF]	1.2 nF [C0603C122K5RACTU]	1.2 nF [C1206C122K2GACTU]
1.2 mH [SRR0906-122YL]	1.2 nF [C0402C122K3HACTU]	1.2 nF [C0805C122K1GACTU]	1.2 nF [C1206C122K2RACTU]
1.2 mH [SRR1005-122K]	1.2 nF [C0402C122K3RACTU]	1.2 nF [C0805C122K1RACTU]	1.2 nF [C1206C122K5GACTU]
1.2 mH [SRR1206-122KL]	1.2 nF [C0402C122K4RACTU]	1.2 nF [C0805C122K2RACTU]	
1.2 MOhm [4116R-1-125LF]	1.2 nF [C0402C122K5HACTU]		

Multisim 14.1 Education Components

1.2 nF [C1210C122KBGAC TU]	1.2 nF [GMC7.3123K400K3 5TR12]	1.2 Ohm [CR1206- J/-1R2ELF]	1.2 uF [C0805C125K4RACT U]
1.2 nF [C1812C122KBGAC TU]	1.2 nF [MMC5.7122K100J 31TR12]	1.2 Ohm [CR2010- J/-1R2ELF]	1.2 uF [C0805C125K8PACT U]
1.2 nF [C1825C122KBGAC TU]	1.2 nF [MMC5.7122K250J 31TR12]	1.2 Ohm [CRL0603- FW-1R20ELF]	1.2 uF [C0805C125K8RACT U]
1.2 nF [C2220C122KBGAC TU]	1.2 nF [MMC5.7122K50J3 1TR12]	1.2 Ohm [CRL0603- JW-1R20ELF]	1.2 uF [C0805C125K9PACT U]
1.2 nF [C2225C122KBGAC TU]	1.2 nF [MMC7.3122K100K 31TR12]	1.2 Ohm [CRL0805- FW-1R20ELF]	1.2 uF [C0805C125K9RACT U]
1.2 nF [GMC5.7122K100J3 1TR12]	1.2 nF [MMC7.3122K250K 31TR12]	1.2 Ohm [CRL1206- FW-1R20ELF]	1.2 uF [C1206C125K3RACT U]
1.2 nF [GMC5.7122K50J31 TR12]	1.2 nF [MMC7.3122K400K 31TR12]	1.2 Ohm [CRL2010- FW-1R20ELF]	1.2 uF [C1206C125K4RACT U]
1.2 nF [GMC5.7123K250J3 3TR12]	1.2 nF [MMC7.3122K50K3 1TR12]	1.2 Ohm [CRL2010- JW-1R20ELF]	1.2 uF [C1206C125K8RACT U]
1.2 nF [GMC7.3122K100K3 1TR12]	1.2 nF [MMC7.3122K63K3 1TR12]	1.2 Ohm [CRL2512- FW-1R20ELF]	1.2 uF [C1210C125K3PACT U]
1.2 nF [GMC7.3122K400K3 1TR12]	1.2 Ohm [CR0402- J/-1R2GLF]	1.2 Ohm [CRM2512-JW- 1R2ELF]	1.2 uF [C1210C125K3RACT U]
1.2 nF [GMC7.3123K100K3 1TR12]	1.2 Ohm [CR0603- J/-1R2ELF]	1.2 Ohm [CRT0402- FZ-1R20GLF]	1.2 uF [C1210C125K3RACT U]
	1.2 Ohm [CR0805- J/-1R2ELF]	1.2 Ohm [PWR6327W1R20F]	1.2 uF [C1210F125K4RACT U]
		1.2 uF [C0805C125K4PACT U]	

Multisim 14.1 Education Components

1.2 uF [C1825C125K5RACT U]	1.2 uF [MDK15125K50B53 P3TUBE]	1.2 uH [SRP4020TA-1R2M]	1.2 uH [SRU6025A- 1R2Y]
1.2 uF [C1825C125M5UAC TU]	1.2 uH [SDE0604A- 1R2M]	1.2 uH [SRP5030T- 1R2M]	1.21 kOhm [CR0402-FX- 1211GLF]
1.2 uF [C2220C125K5RACT U]	1.2 uH [SDR0302- 1R2ML]	1.2 uH [SRP5030TA-1R2M]	1.21 kOhm [CR0603-FX- 1211ELF]
1.2 uF [C2225C125KARACT U]	1.2 uH [SDR0604- 1R2ML]	1.2 uH [SRP7050TA-1R2M]	1.21 kOhm [CR0805-FX- 1211ELF]
1.2 uF [MDC10125K100A5 2P3TUBE]	1.2 uH [SDR0703- 1R2ML]	1.2 uH [SRR1260- 1R2Y]	1.21 kOhm [CR1206-FX- 1211ELF]
1.2 uF [MDC10125K250A5 8P7TUBE]	1.2 uH [SDR7045- 1R2M]	1.2 uH [SRR1260A- 1R2Y]	1.21 kOhm [CR2010-FX- 1211ELF]
1.2 uF [MDC10125K250A5 8P8TUBE]	1.2 uH [SRN3010- 1R2Y]	1.2 uH [SRR1280- 1R2Y]	1.21 kOhm [CRM1206-FX- 1211ELF]
1.2 uF [MDC10125K50A52 P3TUBE]	1.2 uH [SRN4018- 1R2Y]	1.2 uH [SRR4011- 1R2YL]	1.21 kOhm [CRT0402-FZ- 1211GLF]
1.2 uF [MDC15125K100B5 3P3TUBE]	1.2 uH [SRN4026- 1R2Y]	1.2 uH [SRR4028- 1R2Y]	1.21 kOhm [CRT0603-BY- 1211ELF]
1.2 uF [MDC15125K50B53 P3TUBE]	1.2 uH [SRP1040- 1R2M]	1.2 uH [SRR5018- 1R2Y]	1.21 kOhm [CR0402-FX- 1211GLF]
1.2 uF [MDK15125K100B5 3P3TUBE]	1.2 uH [SRP1235- 1R2M]	1.2 uH [SRU3014- 1R2Y]	1.21 kOhm [CR0603-BY- 1211ELF]
1.2 uF [MDK15125K50B53 P3TUBE]	1.2 uH [SRP1250- 1R2M]	1.2 uH [SRU5028- 1R2Y]	1.21 kOhm [CR0805-BY- 1211ELF]
1.2 uF [MDK15125K100B5 3P3TUBE]	1.2 uH [SRP4012- 1R2M]	1.2 uH [SRU5028A- 1R2Y]	1.21 MOhm [CR0402-FX- 1214GLF]
1.2 uF [MDK15125K100B5 3P3TUBE]	1.2 uH [SRP4012TA-1R2M]	1.2 uH [SRU6018- 1R2Y]	
	1.2 uH [SRP4020- 1R2M]	1.2 uH [SRU6025- 1R2Y]	

Multisim 14.1 Education Components

1.21 MOhm [CR0603-FX- 1214ELF]	1.25 uH [SRP1205- 1R0Y]	1.3 kOhm [CAY16- 1301F4LF]	1.3 MOhm [CR0805-JW- 135ELF]
1.21 MOhm [CR0805-FX- 1214ELF]	1.27 kOhm [CR0402-FX- 1271GLF]	1.3 kOhm [CAY16- 132J4LF]	1.3 MOhm [CR1206-FW- 1304ELF]
1.21 Ohm [CRM1206-FX- 1R21ELF]	1.27 kOhm [CR0603-FX- 1271ELF]	1.3 kOhm [CR0402- FX-1301GLF]	1.3 MOhm [CR1206-JW- 135ELF]
1.24 kOhm [CR0402-FX- 1241GLF]	1.27 kOhm [CR0805-FX- 1271ELF]	1.3 kOhm [CR0603- FX-1301ELF]	1.3 nF [C0402C132K3HACT U]
1.24 kOhm [CR0603-FX- 1241ELF]	1.27 kOhm [CR1206-FX- 1271ELF]	1.3 kOhm [CR0603- JW-132ELF]	1.3 nF [C0402C132K5HACT U]
1.24 kOhm [CR0805-FX- 1241ELF]	1.27 kOhm [CRT0603-FZ- 1271ELF]	1.3 kOhm [CR0805- JW-132ELF]	1.3 nF [C0603C132K1HACT U]
1.24 kOhm [CR1206-FX- 1241ELF]	1.27 kOhm [CRT1206-BY- 1271ELF]	1.3 kOhm [CR1206- FX-1301ELF]	1.3 nF [C0603C132K3HACT U]
1.24 kOhm [CR1206-FX- 1241GLF]	1.3 kOhm [4308R- 101-132]	1.3 kOhm [CR1206- JW-132ELF]	1.3 nF [C0603C132K5HACT U]
1.24 kOhm [CRT0402-BV- 1241GLF]	1.3 kOhm [4608M- 102-132LF]	1.3 kOhm [CR2010- JW-132ELF]	1.3 nF [C1210C132KBGAC TU]
1.24 kOhm [CRT0805-CX- 1241ELF]	1.3 kOhm [4816P- 2-132]	1.3 MOhm [CR0402-JW- 135GLF]	1.3 nF [C1812C132KBGAC TU]
1.25 kOhm [PWR220T-35- 1251J]	1.3 kOhm [CAT16- 132J4LF]	1.3 MOhm [CR0603-JW- 135ELF]	1.3 nF [C1825C132KBGAC TU]

Multisim 14.1 Education Components

1.3 nF [C2220C132KBGAC TU]	1.3 Ohm [CRM1206-JW- 1R3ELF]	1.33 kOhm [CRT0805-CX- 1331ELF]	1.4 kOhm [CRT0603-DZ- 1401ELF]
1.3 nF [C2225C132KBGAC TU]	1.3 Ohm [CRM2512-JW- 1R3ELF]	1.33 MOhm [CR0402-FX- 1334GLF]	1.4 kOhm [CRT0805-BY- 1401ELF]
1.3 Ohm [CR0805- J/-1R3ELF]	1.3 Ohm [PWR263S-20- 1R30F]	1.37 kOhm [CAT16- 1371F4LF]	1.4 uH [SDR0302- 1R4ML]
1.3 Ohm [CR1206- J/-1R3ELF]	1.3 uH [SRN6045- 1R3Y]	1.37 kOhm [CR0402-FX- 1371GLF]	1.4 uH [SDR0403- 1R4ML]
1.3 Ohm [CR2010- J/-1R3ELF]	1.3 uH [SRP1204- 1R1M]	1.37 kOhm [CR0603-FX- 1371ELF]	1.4 uH [SRP1045- 1R4M]
1.3 Ohm [CRL0603- FW-1R30ELF]	1.33 kOhm [CR0402-FX- 1331GLF]	1.37 kOhm [CR0805-FX- 1371ELF]	1.4 uH [SRR1280- 1R4Y]
1.3 Ohm [CRL0603- JW-1R30ELF]	1.33 kOhm [CR0603-FX- 1331ELF]	1.37 kOhm [CR1206-FX- 1371ELF]	1.4 uH [SRR1305- 1R4ZL]
1.3 Ohm [CRL0805- FW-1R30ELF]	1.33 kOhm [CR0805-FX- 1331ELF]	1.4 kOhm [4116R- 1-142]	1.43 kOhm [CR0402-FX- 1431GLF]
1.3 Ohm [CRL0805- JW-1R30ELF]	1.33 kOhm [CR1206-FX- 1331ELF]	1.4 kOhm [CR0402- FX-1401GLF]	1.43 kOhm [CR0603-FX- 1431ELF]
1.3 Ohm [CRL1206- FW-1R30ELF]	1.33 kOhm [CRT0402-FZ- 1331GLF]	1.4 kOhm [CR0603- FX-1401ELF]	1.43 kOhm [CR0805-FX- 1431ELF]
1.3 Ohm [CRL1206- JW-1R30ELF]	1.33 kOhm [CRT0603-BY- 1331ELF]	1.4 kOhm [CR1206- FX-1401ELF]	1.43 kOhm [CR1206-FX- 1431ELF]
1.3 Ohm [CRL2010- FW-1R30ELF]	1.33 kOhm [CRT0805-BY- 1331ELF]	1.4 kOhm [CRT0603-BY- 1401ELF]	1.47 kOhm [CR0402-FX- 1471GLF]
1.3 Ohm [CRL2010- JW-1R30ELF]			
1.3 Ohm [CRL2512- FW-1R30ELF]			

Multisim 14.1 Education Components

1.47 kOhm [CR0603-FX- 1471ELF]	1.5 kOhm [4116R- 2-152]	1.5 kOhm [4308R- 102-152]	1.5 kOhm [4416P- T01-152]
1.47 kOhm [CR0805-FX- 1471ELF]	1.5 kOhm [4116R- 2-152LF]	1.5 kOhm [4308R- 102-152LF]	1.5 kOhm [4420P- 1-152]
1.47 kOhm [CR1206-FX- 1471ELF]	1.5 kOhm [4306H- 101-152LF]	1.5 kOhm [4309R- 101-152]	1.5 kOhm [4420P- 2-152]
1.47 kOhm [CR1206-FX- 1471ELF]	1.5 kOhm [4306M- 101-152]	1.5 kOhm [4309R- 101-152LF]	1.5 kOhm [4420P- T01-152]
1.47 kOhm [CRT0402-FZ- 1471GLF]	1.5 kOhm [4306M- 101-152LF]	1.5 kOhm [4310H- 101-152LF]	1.5 kOhm [4420P- T02-152]
1.47 kOhm [CRT0603-FZ- 1471ELF]	1.5 kOhm [4306R- 101-152]	1.5 kOhm [4310H- 102-152]	1.5 kOhm [4604X- 101-152LF]
1.47 kOhm [CRT0603-FZ- 1471ELF]	1.5 kOhm [4306R- 101-152LF]	1.5 kOhm [4310H- 102-152LF]	1.5 kOhm [4604X- 102-152LF]
1.47 kOhm [CRT0603-PW- 1471ELF]	1.5 kOhm [4306R- 102-152]	1.5 kOhm [4310M- 101-152]	1.5 kOhm [4605X- 101-152LF]
1.47 MOhm [CR1206-FW- 1474ELF]	1.5 kOhm [4306R- 102-152LF]	1.5 kOhm [4310M- 101-152LF]	1.5 kOhm [4605X- AP1-152LF]
1.5 kOhm [4114R- 1-152]	1.5 kOhm [4308H- 102-152]	1.5 kOhm [4310M- 102-152]	1.5 kOhm [4606X- 101-152LF]
1.5 kOhm [4114R- 1-152LF]	1.5 kOhm [4308H- 102-152LF]	1.5 kOhm [4310R- 101-152]	1.5 kOhm [4606X- 102-152LF]
1.5 kOhm [4114R- 2-152]	1.5 kOhm [4308M- 101-152]	1.5 kOhm [4310R- 101-152LF]	1.5 kOhm [4606X- AP2-152LF]
1.5 kOhm [4114R- 2-152LF]	1.5 kOhm [4308M- 101-152LF]	1.5 kOhm [4310R- 102-152]	1.5 kOhm [4607X- 101-152LF]
1.5 kOhm [4116R- 1-152]	1.5 kOhm [4308R- 101-152]	1.5 kOhm [4310R- 102-152LF]	1.5 kOhm [4608H- 102-152LF]
1.5 kOhm [4116R- 1-152LF]	1.5 kOhm [4308R- 101-152LF]	1.5 kOhm [4416P- 2-152]	1.5 kOhm [4608M- 102-152LF]

Multisim 14.1 Education Components

1.5 kOhm [4608X-101-152LF]	1.5 kOhm [4614X-102-152LF]	1.5 kOhm [4820P-1-152]	1.5 kOhm [CR0201-JW-152GLF]
1.5 kOhm [4608X-102-152LF]	1.5 kOhm [4814P-1-152LF]	1.5 kOhm [4820P-2-152]	1.5 kOhm [CR0402-FX-1501GLF]
1.5 kOhm [4608X-AP1-152LF]	1.5 kOhm [4814P-2-152]	1.5 kOhm [4820P-T01-152]	1.5 kOhm [CR0402-JW-152GLF]
1.5 kOhm [4608X-AP2-152LF]	1.5 kOhm [4814P-2-152LF]	1.5 kOhm [4820P-T01-152LF]	1.5 kOhm [CR0603-FX-1501ELF]
1.5 kOhm [4609H-101-152LF]	1.5 kOhm [4814P-T01-152]	1.5 kOhm [4820P-T02-152]	1.5 kOhm [CR0603-JW-152ELF]
1.5 kOhm [4609X-101-152LF]	1.5 kOhm [4814P-T01-152LF]	1.5 kOhm [CAT10-152J4LF]	1.5 kOhm [CR0603-JW-152GLF]
1.5 kOhm [4609X-AP1-152LF]	1.5 kOhm [4814P-T02-152]	1.5 kOhm [CAT16-1501F4LF]	1.5 kOhm [CR0805-FX-1501ELF]
1.5 kOhm [4610H-101-152LF]	1.5 kOhm [4814P-T02-152LF]	1.5 kOhm [CAT16-152J4LF]	1.5 kOhm [CR0805-FX-1501GLF]
1.5 kOhm [4610H-102-152LF]	1.5 kOhm [4816P-1-152]	1.5 kOhm [CAT25-152JALF]	1.5 kOhm [CR0805-JW-152ELF]
1.5 kOhm [4610X-101-152LF]	1.5 kOhm [4816P-1-152LF]	1.5 kOhm [CAY10-152J4LF]	1.5 kOhm [CR0805-JW-152GLF]
1.5 kOhm [4610X-102-152LF]	1.5 kOhm [4816P-2-152]	1.5 kOhm [CAY16-1501F4LF]	1.5 kOhm [CR1206-FX-1501ELF]
1.5 kOhm [4610X-AP1-152LF]	1.5 kOhm [4816P-2-152LF]	1.5 kOhm [CAY16-152J2LF]	1.5 kOhm [CR1206-FX-1501GLF]
1.5 kOhm [4611X-101-152LF]	1.5 kOhm [4816P-T01-152LF]	1.5 kOhm [CAY16-152J4LF]	1.5 kOhm [CR1206-JW-152ELF]
1.5 kOhm [4612X-101-152LF]	1.5 kOhm [4816P-T02-152]	1.5 kOhm [CAY16-152J8LF]	1.5 kOhm [CR1206-JW-152GLF]
1.5 kOhm [4613X-101-152LF]	1.5 kOhm [4816P-T02-152LF]	1.5 kOhm [CAY17-152JALF]	1.5 kOhm [CR2010-JW-152ELF]

Multisim 14.1 Education Components

1.5 kOhm [CR2512-FX-1501ELF]	1.5 kOhm [CRT0805-BY-1501ELF]	1.5 mF [T530X158M003AT E008]	1.5 mH [SRE6603-152M]
1.5 kOhm [CR2512-JW-152ELF]	1.5 kOhm [PWR220T-35-1501J]	1.5 mF [T530X158M2R5AT E005]	1.5 mH [SRR0906-152YL]
1.5 kOhm [CRM1206-FX-1501ELF]	1.5 kOhm [PWR221T-30-1501F]	1.5 mF [TAJE158K002RNJ]	1.5 mH [SRR0908-152YL]
1.5 kOhm [CRM2512-FX-1501ELF]	1.5 kOhm [PWR2615W1501J]	1.5 mF [TPME158K002R00 12]	1.5 mH [SRR1005-152K]
1.5 kOhm [CRM2512-JW-152ELF]	1.5 kOhm [PWR2615W1501JE]]	1.5 mF [TPME158K002R00 15]	1.5 mH [SRR1206-152KL]
1.5 kOhm [CRT0402-BW-1501GLF]	1.5 kOhm [PWR263S-35-1501F]	1.5 mF [TPME158K002R00 18]	1.5 mH [SRR1208-152KL]
1.5 kOhm [CRT0402-BY-1501GLF]	1.5 kOhm [PWR4525W1501J]	1.5 mF [TPME158K004R00 18]	1.5 mH [SRR6603-152ML]
1.5 kOhm [CRT0603-BY-1501ELF]	1.5 kOhm [PWR4525W1501JE]]	1.5 mF [TRME158K002R00 18]	1.5 MOhm [4606X-102-155LF]
1.5 kOhm [CRT0603-DY-1501ELF]	1.5 kOhm [PWR6327W1501J]	1.5 mH [SDR0503-152JL]	1.5 MOhm [CAT25-155JALF]
1.5 kOhm [CRT0603-FX-1501ELF]	1.5 kOhm [PWR6327W1501JE]]	1.5 mH [SDR0805-152KL]	1.5 MOhm [CR0402-FX-1504GLF]
1.5 kOhm [CRT0603-PV-1501ELF]	1.5 mF [2R5TPE1500MC]	1.5 mH [SDR0906-152KL]	1.5 MOhm [CR0402-JW-155GLF]
1.5 kOhm [CRT0805-BX-1501ELF]	1.5 mF [2R5TPE1500MF]	1.5 mH [SDR1005-152KL]	1.5 MOhm [CR0603-FX-1504ELF]
		1.5 mH [SDR1006-152KL]	1.5 MOhm [CR0603-JW-155ELF]

Multisim 14.1 Education Components

1.5 MOhm [CR0805-FX- 1504ELF]	1.5 nF [C0402C152K8RACT U]	1.5 nF [C0805C152K1RACT U]	1.5 nF [C1206C152K2RACT U]
1.5 MOhm [CR0805-JW- 155ELF]	1.5 nF [C0603C152K1HACT U]	1.5 nF [C0805C152K2RACT U]	1.5 nF [C1206C152K5GACT U]
1.5 MOhm [CR1206-FW- 1504ELF]	1.5 nF [C0603C152K1RACT U]	1.5 nF [C0805C152K3RACT U]	1.5 nF [C1206C152K5RACT U]
1.5 MOhm [CR1206-JW- 155ELF]	1.5 nF [C0603C152K2RACT U]	1.5 nF [C0805C152K4GACT U]	1.5 nF [C1210C152K1GACT U]
1.5 MOhm [CRT0805-DZ- 1504ELF]	1.5 nF [C0603C152K3HACT U]	1.5 nF [C0805C152K4RACT U]	1.5 nF [C1210C152K5GACT U]
1.5 mOhm [CST0612-FC- R0015E]	1.5 nF [C0603C152K3RACT U]	1.5 nF [C0805C152K5GACT U]	1.5 nF [C1210C152KBGAC TU]
1.5 nF [C0402C152K3HACT U]	1.5 nF [C0603C152K4RACT U]	1.5 nF [C0805C152K5RACT U]	1.5 nF [C1812C152K2GACT U]
1.5 nF [C0402C152K3RACT U]	1.5 nF [C0603C152K5HACT U]	1.5 nF [C0805C152KARACT U]	1.5 nF [C1812C152KBGAC TU]
1.5 nF [C0402C152K4RACT U]	1.5 nF [C0603C152K5RACT U]	1.5 nF [C1206C152K1GACT U]	1.5 nF [C1825C152KBGAC TU]
1.5 nF [C0402C152K5HACT U]	1.5 nF [C0603C152K8RACT U]	1.5 nF [C1206C152K1RACT U]	1.5 nF [C2220C152KBGAC TU]
1.5 nF [C0402C152K5RACT U]	1.5 nF [C0805C152K1GACT U]	1.5 nF [C1206C152K2GACT U]	1.5 nF [C2225C152KBGAC TU]

Multisim 14.1 Education Components

1.5 nF [CDR04BP152BKSM]	1.5 nF [MMC5.7152K100J 31TR12]	1.5 nF [SPC7.3152K630K31 TR12]	1.5 Ohm [CRL2512- FW-1R50ELF]
1.5 nF [GMC5.7152K100J3 1TR12]	1.5 nF [MMC5.7152K250J 31TR12]	1.5 Ohm [CR0402- J/-1R5GLF]	1.5 Ohm [CRM0805-JW- 1R5ELF]
1.5 nF [GMC5.7152K50J31 TR12]	1.5 nF [MMC5.7152K50J3 1TR12]	1.5 Ohm [CR0603- J/-1R5ELF]	1.5 Ohm [CRM1206-FX- 1R50ELF]
1.5 nF [GMC5.7153K250J3 3TR12]	1.5 nF [MMC7.3152K100K 31TR12]	1.5 Ohm [CR0805- J/-1R5ELF]	1.5 Ohm [CRM2010-FX- 1R50ELF]
1.5 nF [GMC7.3152K100K3 1TR12]	1.5 nF [MMC7.3152K250K 31TR12]	1.5 Ohm [CR1206- J/-1R5ELF]	1.5 Ohm [CRM2512-JW- 1R5ELF]
1.5 nF [GMC7.3152K400K3 1TR12]	1.5 nF [MMC7.3152K400K 31TR12]	1.5 Ohm [CR2512- J/-1R5ELF]	1.5 Ohm [PWR163S-25- 1R50F]
1.5 nF [GMC7.3153K100K3 1TR12]	1.5 nF [MMC7.3152K50K3 1TR12]	1.5 Ohm [CRL0603- FW-1R50ELF]	1.5 Ohm [PWR163S-25- 1R50FE]
1.5 nF [GMC7.3153K400K3 7TR12]	1.5 nF [MMC7.3152K63K3 1TR12]	1.5 Ohm [CRL0805- FW-1R50ELF]	1.5 Ohm [PWR163S-25- 1R50J]
1.5 nF [GPC7.3152K160K3 1TR12]	1.5 nF [SPC7.3152K100K31 TR12]	1.5 Ohm [CRL0805- JW-1R50ELF]	1.5 Ohm [PWR220T-20- 1R50F]
1.5 nF [GPC7.3152K630K3 1TR12]	1.5 nF [SPC7.3152K250K31 TR12]	1.5 Ohm [CRL1206- FW-1R50ELF]	1.5 Ohm [PWR220T-20- 1R50J]
1.5 nF [GPC7.3152K63K31 TR12]	1.5 nF [SPC7.3152K400K31 TR12]	1.5 Ohm [CRL2010- FW-1R50ELF]	1.5 Ohm [PWR220T-35- 1R50J]

Multisim 14.1 Education Components

1.5 Ohm [PWR221T-30-1R50F]	1.5 Ohm [PWR4525W1R50JE]	1.5 uF [C1206C155K4RACTU]	1.5 uF [C2225C155K5RACTU]
1.5 Ohm [PWR2615W1R50F]	1.5 Ohm [PWR6327N1R50F]	1.5 uF [C1206C155K8PACTU]	1.5 uF [C2225C155M5UAC TU]
1.5 Ohm [PWR2615W1R50FE]	1.5 Ohm [PWR6327W1R50F]	1.5 uF [C1206C155K8RACTU]	1.5 uF [MDC10155K100A52P3TUBE]
1.5 Ohm [PWR2615W1R50J]	1.5 uF [05086D155KAT2A]	1.5 uF [C1206C155K9RACTU]	1.5 uF [MDC10155K250A58P7TUBE]
1.5 Ohm [PWR263S-20-1R50F]	1.5 uF [C0805C155K4PACTU]	1.5 uF [C1210C155K3PACTU]	1.5 uF [MDC10155K250A58P8TUBE]
1.5 Ohm [PWR263S-20-1R50J]	1.5 uF [C0805C155K4RACTU]	1.5 uF [C1210C155K3RACTU]	1.5 uF [MDC10155K50A52P3TUBE]
1.5 Ohm [PWR263S-20-1R50JE]	1.5 uF [C0805C155K8PACTU]	1.5 uF [C1210C155K4RACTU]	1.5 uF [MDC15155K100B53P3TUBE]
1.5 Ohm [PWR263S-35-1R50F]	1.5 uF [C0805C155K8RACTU]	1.5 uF [C1210F155K4RACTU]	1.5 uF [MDC15155K50B53P3TUBE]
1.5 Ohm [PWR263S-35-1R50J]	1.5 uF [C0805C155K9PACTU]	1.5 uF [C1825C155K5RACTU]	1.5 uF [MDK10155K50A52P3TUBE]
1.5 Ohm [PWR3014WA1R50JE]	1.5 uF [C0805C155K9RACTU]	1.5 uF [C1825C155M5UAC TU]	1.5 uF [MDS10155K100A52P3TUBE]
1.5 Ohm [PWR4525W1R50F]	1.5 uF [C1206C155K3RACTU]	1.5 uF [C2220C155K5RACTU]	1.5 uF [MDS10155K50A52P3TUBE]
1.5 Ohm [PWR4525W1R50J]	1.5 uF [C1206C155K4PACTU]		

Multisim 14.1 Education Components

1.5 uF [MDS15155K100B5 3P3TUBE]	1.5 uF [T494A155M016AT]	1.5 uF [TAJA155K025RNJ]	1.5 uF [TAJT155K020RNJ]
1.5 uF [T419A155M015AH 4250]	1.5 uF [T494A155M025AT]	1.5 uF [TAJA155K035RNJ]	1.5 uF [TAJT155K025RNJ]
1.5 uF [T489C155M050AT E1K5]	1.5 uF [T494B155M025AT]	1.5 uF [TAJB155K025RNJ]	1.5 uF [TAJT155K035RNJ]
1.5 uF [T491A155M010AT]	1.5 uF [T494B155M035AT]	1.5 uF [TAJB155K035RNJ]	1.5 uF [THJA155K020RJN]
1.5 uF [T491A155M016AT]	1.5 uF [T494C155M035AT]	1.5 uF [TAJC155K035RNJ]	1.5 uF [THJC155K035RJN]
1.5 uF [T491A155M020AT]	1.5 uF [T494C155M050AT]	1.5 uF [TAJC155K050RNJ]	1.5 uF [TPSA155K025R300 0]
1.5 uF [T491A155M025AT]	1.5 uF [T494D155M050AT]	1.5 uF [TAJD155K050RNJ]	1.5 uF [TPSB155K025R180 0]
1.5 uF [T491A155M025AT]	1.5 uF [T494S155M020AT]	1.5 uF [TAJP155K025RNJ]	1.5 uF [TPSB155K035R250 0]
1.5 uF [T491B155M025AT]	1.5 uF [T498C155M035AT E3K3]	1.5 uF [TAJR155K006RNJ]	1.5 uF [TPSC155K050R150 0]
1.5 uF [T491B155M035AT]	1.5 uF [TACL155K004RTA]	1.5 uF [TAJR155K010RNJ]	1.5 uF [TPSC155K050R200 0]
1.5 uF [T491C155M035AT]	1.5 uF [TACL155K006RTA]	1.5 uF [TAJR155K016RNJ]	1.5 uF [TPSC155K050R200 0]
1.5 uF [T491C155M050AT]	1.5 uF [TACL155K010RTA]	1.5 uF [TAJS155K006RNJ]	1.5 uF [TRJA155K025RRJ]
1.5 uF [T491D155M050AT]	1.5 uF [TAJA155K010RNJ]	1.5 uF [TAJS155K010RNJ]	1.5 uF [TRJA155K035RRJ]
1.5 uF [T491S155M020AT]	1.5 uF [TAJA155K016RNJ]	1.5 uF [TAJS155K016RNJ]	1.5 uH [SDE0604A- 1R5M]
1.5 uF [T494A155M010AT]	1.5 uF [TAJA155K020RNJ]		

Multisim 14.1 Education Components

1.5 uH [SDE0805A-1R5M]	1.5 uH [SRN3010-1R5Y]	1.5 uH [SRP1270-1R5M]	1.5 uH [SRR0908-1R5ML]
1.5 uH [SDE1006A-1R5M]	1.5 uH [SRN3015-1R5Y]	1.5 uH [SRP1770TA-1R5M]	1.5 uH [SRR1005-1R5M]
1.5 uH [SDR0302-1R5ML]	1.5 uH [SRN4012T-1R5M]	1.5 uH [SRP4012-1R5M]	1.5 uH [SRR1240-1R5Y]
1.5 uH [SDR0603-1R5ML]	1.5 uH [SRN4018-1R5Y]	1.5 uH [SRP4012TA-1R5M]	1.5 uH [SRR1260-1R5Y]
1.5 uH [SDR0604-1R5ML]	1.5 uH [SRN5020-1R5Y]	1.5 uH [SRP4020-1R5M]	1.5 uH [SRR1260A-1R5Y]
1.5 uH [SDR0805-1R5ML]	1.5 uH [SRN5040-1R5Y]	1.5 uH [SRP4020TA-1R5M]	1.5 uH [SRR3011-1R5YL]
1.5 uH [SDR1005-1R5ML]	1.5 uH [SRN6028-1R5Y]	1.5 uH [SRP5015TA-1R5M]	1.5 uH [SRR4011-1R5YL]
1.5 uH [SDR1006-1R5ML]	1.5 uH [SRN8040-1R5Y]	1.5 uH [SRP5030T-1R5M]	1.5 uH [SRR6028-1R5Y]
1.5 uH [SDR1307-1R5ML]	1.5 uH [SRP1038A-1R5M]	1.5 uH [SRP5030TA-1R5M]	1.5 uH [SRR6603-1R5ML]
1.5 uH [SDR1307A-1R5M]	1.5 uH [SRP1040-1R5M]	1.5 uH [SRP6540-1R5M]	1.5 uH [SRU1028-1R5Y]
1.5 uH [SDR6603-1R5M]	1.5 uH [SRP1206-1R3Z]	1.5 uH [SRP7028A-1R5M]	1.5 uH [SRU1028A-1R5Y]
1.5 uH [SDR7030-1R5M]	1.5 uH [SRP1235-1R5M]	1.5 uH [SRP7030-1R5FM]	1.5 uH [SRU1038-1R5Y]
1.5 uH [SDR7045-1R5M]	1.5 uH [SRP1245A-1R5M]	1.5 uH [SRP7050TA-1R5M]	1.5 uH [SRU1038A-1R5Y]
1.5 uH [SRN2012-1R5M]	1.5 uH [SRP1250-1R5M]	1.5 uH [SRR0603-1R5ML]	1.5 uH [SRU1048-1R5Y]
1.5 uH [SRN2512-1R5M]	1.5 uH [SRP1265A-1R5M]	1.5 uH [SRR0604-1R5ML]	1.5 uH [SRU1048A-1R5Y]

Multisim 14.1 Education Components

1.5 uH [SRU3011-1R5Y]	1.58 kOhm [CR1206-FX-1581ELF]	1.5KE39CA-E3/54	1.5SMC6.8A/57T
1.5 uH [SRU3014-1R5Y]	1.58 kOhm [CRT0402-BY-1581GLF]	1.5KE47A-E3/54	1.5SMC6.8AT3G
1.5 uH [SRU5011-1R5Y]	1.58 kOhm [CRT0805-BY-1581GLF]	1.5KE47AG	1.5SMC6.8CA-E3/57T
1.5 uH [SRU5018-1R5Y]	1.58 kOhm [CRT0805-BY-1581ELF]	1.5KE47ARL4G	1.5SMC62AT3G
1.54 kOhm [CR0402-FX-1541GLF]	1.5KA27AHE3/54	1.5KE51CA-E3/54	1.5SMC75CA-E3/57T
1.54 kOhm [CR0603-FX-1541ELF]	1.5KE100A-E3/54	1.5KE91A-E3/54	1.5SMC91AT3G
1.54 kOhm [CR0805-FX-1541ELF]	1.5KE100CA-E3/54	1.5KE91ARL4G	1.6 kOhm [4116R-2-162]
1.54 kOhm [CR1206-FX-1541ELF]	1.5KE110CA-E3/54	1.5SMC12AT3G	1.6 kOhm [4308H-101-162]
1.54 kOhm [CRT0805-BY-1541ELF]	1.5KE12A-E3/54	1.5SMC13A-E3/57T	1.6 kOhm [4308M-102-162]
1.54 kOhm [CR0402-FX-1541GLF]	1.5KE12CA-E3/54	1.5SMC15AT3G	1.6 kOhm [4308M-102-162LF]
1.54 kOhm [CR1206-FX-1541ELF]	1.5KE130CA-E3/54	1.5SMC15CA-E3/57T	1.6 kOhm [4308M-102-162J4LF]
1.54 kOhm [CRT0805-BY-1541ELF]	1.5KE160CA-E3/54	1.5SMC180A-E3/57T	1.6 kOhm [CAT16-162J4LF]
1.58 kOhm [CR0402-FX-1581GLF]	1.5KE180A-E3/54	1.5SMC18CA-E3/57T	1.6 kOhm [CAY16-162J4LF]
1.58 kOhm [CR0603-FX-1581ELF]	1.5KE18A-E3/54	1.5SMC18AT3G	1.6 kOhm [CR0402-FX-1601GLF]
1.58 kOhm [CR0805-FX-1581ELF]	1.5KE200A-E3/54	1.5SMC20AT3G	1.6 kOhm [CR0603-FX-1601ELF]
1.58 kOhm [CR1206-FX-1581ELF]	1.5KE200CA-E3/54	1.5SMC24AT3G	1.6 kOhm [CR0603-JW-162ELF]
1.58 kOhm [CR0402-FX-1581GLF]	1.5KE20A-E3/51	1.5SMC33AT3G	1.6 kOhm [CR0805-FX-1601ELF]
1.58 kOhm [CR0603-FX-1581ELF]	1.5KE220CA-E3/54	1.5SMC39A-E3/57T	1.6 kOhm [CR0805-JW-162ELF]
1.58 kOhm [CR0805-FX-1581ELF]	1.5KE24CA-E3/54	1.5SMC39AT3G	
	1.5KE36A-E3/54	1.5SMC43AT3G	
	1.5KE36CA-E3/54	1.5SMC540A-E3/57T	
	1.5KE39ARL4G		

Multisim 14.1 Education Components

1.6 kOhm [CR1206-FX-1601ELF]	1.6 nF [C1812C162KBGAC TU]	1.6 Ohm [CRL2010-FW-1R60ELF]	1.65 kOhm [CR0805-FX-1651ELF]
1.6 kOhm [CR1206-JW-162ELF]	1.6 nF [C1825C162KBGAC TU]	1.6 Ohm [CRL2010-JW-1R60ELF]	1.65 kOhm [CR1206-FX-1651ELF]
1.6 MOhm [CR0603-JW-165ELF]	1.6 nF [C2220C162KBGAC TU]	1.6 Ohm [CRL2512-FW-1R60ELF]	1.65 kOhm [CRT0603-PW-1651ELF]
1.6 MOhm [CR0805-JW-165ELF]	1.6 nF [C2225C162KBGAC TU]	1.62 kOhm [CR0402-FX-1621GLF]	1.65 kOhm [CRT1206-BY-1651ELF]
1.6 MOhm [CR1206-FW-1604ELF]	1.6 Ohm [CR0402-J/-1R6GLF]	1.62 kOhm [CR0603-FX-1621ELF]	1.69 kOhm [CAT16-1691F4LF]
1.6 MOhm [CR1206-JW-165ELF]	1.6 Ohm [CR0603-J/-1R6ELF]	1.62 kOhm [CR0805-FX-1621ELF]	1.69 kOhm [CR0402-FX-1691GLF]
1.6 nF [C0603C162K1HACT U]	1.6 Ohm [CR0805-J/-1R6ELF]	1.62 kOhm [CR1206-FX-1621ELF]	1.69 kOhm [CR0603-FX-1691ELF]
1.6 nF [C0603C162K3HACT U]	1.6 Ohm [CRL0603-FW-1R60ELF]	1.62 kOhm [CR2010-FX-1621ELF]	1.69 kOhm [CR0805-FX-1691ELF]
1.6 nF [C0603C162K5HACT U]	1.6 Ohm [CRL0603-JW-1R60ELF]	1.62 kOhm [CRT0402-FZ-1621GLF]	1.69 kOhm [CR1206-FX-1691ELF]
1.6 nF [C0805C162K4GACT U]	1.6 Ohm [CRL0805-FW-1R60ELF]	1.65 kOhm [CR0402-FX-1651GLF]	1.69 kOhm [CRT0402-BW-1691GLF]
1.6 nF [C1206C162K5GACT U]	1.6 Ohm [CRL1206-FW-1R60ELF]	1.65 kOhm [CR0603-FX-1651ELF]	
1.6 nF [C1210C162KBGAC TU]	1.6 Ohm [CRL1206-JW-1R60ELF]		

Multisim 14.1 Education Components

1.69 kOhm [CRT1206-BY- 1691ELF]	1.78 kOhm [CR0805-FX- 1781ELF]	1.8 kOhm [4306M- 102-182]	1.8 kOhm [4310H- 102-182LF]
1.7 uH [SRP1040- 1R7M]	1.78 kOhm [CR1206-FX- 1781ELF]	1.8 kOhm [4306M- 102-182LF]	1.8 kOhm [4310M- 101-182]
1.74 kOhm [CR0402-FX- 1741GLF]	1.78 kOhm [CRT0402-FZ- 1781GLF]	1.8 kOhm [4306R- 101-182]	1.8 kOhm [4310M- 102-182]
1.74 kOhm [CR0603-FX- 1741ELF]	1.78 kOhm [CRT1206-DX- 1781ELF]	1.8 kOhm [4306R- 102-182]	1.8 kOhm [4310R- 101-182]
1.74 kOhm [CR0805-FX- 1741ELF]	1.78 MOhm [CR1206-FW- 1784ELF]	1.8 kOhm [4306R- 102-182LF]	1.8 kOhm [4310R- 101-182LF]
1.74 kOhm [CR1206-FX- 1741ELF]	1.8 kOhm [4114R- 1-182]	1.8 kOhm [4308M- 102-182]	1.8 kOhm [4310R- 102-182]
1.74 kOhm [CRT0603-BY- 1741ELF]	1.8 kOhm [4114R- 1-182LF]	1.8 kOhm [4308M- 102-182LF]	1.8 kOhm [4310R- 102-182LF]
1.74 MOhm [CR0805-FX- 1744ELF]	1.8 kOhm [4114R- 2-182]	1.8 kOhm [4308R- 101-182]	1.8 kOhm [4420P- T02-182]
1.74 MOhm [CR0805-FX- 1744ELF]	1.8 kOhm [4114R- 2-182LF]	1.8 kOhm [4308R- 101-182LF]	1.8 kOhm [4604X- 102-182LF]
1.74 Ohm [CRT1206-DZ- 1R74ELF]	1.8 kOhm [4114R- 2-182LF]	1.8 kOhm [4308R- 102-182]	1.8 kOhm [4605X- 101-182LF]
1.74 Ohm [CRT1206-DZ- 1R74ELF]	1.8 kOhm [4116R- 1-182]	1.8 kOhm [4308R- 102-182LF]	1.8 kOhm [4606H- 101-182LF]
1.78 kOhm [CR0402-FX- 1781GLF]	1.8 kOhm [4116R- 1-182LF]	1.8 kOhm [4308R- 102-182LF]	1.8 kOhm [4606H- 101-182LF]
1.78 kOhm [CR0402-FX- 1781GLF]	1.8 kOhm [4116R- 1-182LF]	1.8 kOhm [4309R- 101-182]	1.8 kOhm [4606X- 101-182LF]
1.78 kOhm [CR0603-FX- 1781ELF]	1.8 kOhm [4116R- 2-182]	1.8 kOhm [4309R- 101-182LF]	1.8 kOhm [4606X- 102-182LF]
1.78 kOhm [CR0603-FX- 1781ELF]	1.8 kOhm [4116R- 2-182LF]	1.8 kOhm [4309R- 101-182LF]	1.8 kOhm [4606X- 102-182LF]
1.78 kOhm [CR0603-FX- 1781ELF]	1.8 kOhm [4116R- 2-182LF]	1.8 kOhm [4310H- 102-182]	1.8 kOhm [4607X- 101-182LF]

Multisim 14.1 Education Components

1.8 kOhm [4608H-102-182LF]	1.8 kOhm [4816P-T01-182]	1.8 kOhm [CR0603-FX-1801ELF]	1.8 kOhm [CRM2512-JW-182ELF]
1.8 kOhm [4608M-102-182LF]	1.8 kOhm [4816P-T01-182LF]	1.8 kOhm [CR0603-FX-1801GLF]	1.8 kOhm [CRT0603-BX-1801ELF]
1.8 kOhm [4608X-101-182LF]	1.8 kOhm [4816P-T02-182]	1.8 kOhm [CR0603-JW-182ELF]	1.8 kOhm [CRT0603-BY-1801ELF]
1.8 kOhm [4608X-102-182LF]	1.8 kOhm [4816P-T02-182LF]	1.8 kOhm [CR0805-FX-1801ELF]	1.8 kOhm [CRT0805-BY-1801ELF]
1.8 kOhm [4608X-AP1-182LF]	1.8 kOhm [4820P-2-182]	1.8 kOhm [CR0805-FX-1801GLF]	1.8 kOhm [CRT0805-DY-1801ELF]
1.8 kOhm [4608X-AP2-182LF]	1.8 kOhm [CAT16-1801F4LF]	1.8 kOhm [CR0805-JW-182ELF]	1.8 kOhm [CRT0805-DY-1801ELF]
1.8 kOhm [4609X-101-182LF]	1.8 kOhm [CAT16-182J4LF]	1.8 kOhm [CR0805-JW-182GLF]	1.8 kOhm [CRT0805-FX-1801ELF]
1.8 kOhm [4610H-101-182LF]	1.8 kOhm [CAT25-182JALF]	1.8 kOhm [CR1206-FX-1801ELF]	1.8 mH [SDR0503-182JL]
1.8 kOhm [4610X-101-182LF]	1.8 kOhm [CAY10-182J4LF]	1.8 kOhm [CR1206-JW-182ELF]	1.8 mH [SDR0805-182KL]
1.8 kOhm [4610X-102-182LF]	1.8 kOhm [CAY16-1801F4LF]	1.8 kOhm [CR1206-JW-182GLF]	1.8 mH [SDR0906-182KL]
1.8 kOhm [4612X-102-182LF]	1.8 kOhm [CAY16-182J4LF]	1.8 kOhm [CR2512-JW-182ELF]	1.8 mH [SDR1006-182KL]
1.8 kOhm [4816P-1-182]	1.8 kOhm [CAY16-182J8LF]	1.8 kOhm [CRM1206-FX-1801ELF]	1.8 mH [SRR0906-182YL]
1.8 kOhm [4816P-1-182LF]	1.8 kOhm [CAY17-182JALF]	1.8 kOhm [CRM1206-JW-182ELF]	1.8 mH [SRR1005-182K]
1.8 kOhm [4816P-2-182]	1.8 kOhm [CR0402-FX-1801GLF]	1.8 kOhm [CRM2010-JW-182ELF]	1.8 mH [SRR1208-182KL]
1.8 kOhm [4816P-2-182LF]	1.8 kOhm [CR0402-JW-182GLF]		

Multisim 14.1 Education Components

1.8 MOhm [4310R-101-185]	1.8 nF [C0603C182K3HACT U]	1.8 nF [C1206C182K1GACT U]	1.8 nF [C2220C182KBGAC TU]
1.8 MOhm [CAT25-185JALF]	1.8 nF [C0603C182K3RACT U]	1.8 nF [C1206C182K1RACT U]	1.8 nF [C2225C182KBGAC TU]
1.8 MOhm [CHV0805-FX-1804ELF]	1.8 nF [C0603C182K5HACT U]	1.8 nF [C1206C182K2GACT U]	1.8 nF [GMC5.7182K100J3 1TR12]
1.8 MOhm [CR0603-JW-185ELF]	1.8 nF [C0603C182K5RACT U]	1.8 nF [C1206C182K5GACT U]	1.8 nF [GMC5.7182K50J31 TR12]
1.8 MOhm [CR0805-FX-1804ELF]	1.8 nF [C0805C182K1GACT U]	1.8 nF [C1206C182K5RACT U]	1.8 nF [GMC5.7183K250J3 3TR12]
1.8 MOhm [CR0805-JW-185ELF]	1.8 nF [C0805C182K1RACT U]	1.8 nF [C1210C182K1GACT U]	1.8 nF [GMC7.3182K100K3 1TR12]
1.8 MOhm [CR1206-FW-1804ELF]	1.8 nF [C0805C182K2RACT U]	1.8 nF [C1210C182K2GACT U]	1.8 nF [GMC7.3182K400K3 1TR12]
1.8 MOhm [CR1206-JW-185ELF]	1.8 nF [C0805C182K4RACT U]	1.8 nF [C1210C182K5GACT U]	1.8 nF [GMC7.3183K100K3 1TR12]
1.8 nF [C0402C182K3RACT U]	1.8 nF [C0805C182K5GACT U]	1.8 nF [C1210C182KBGAC TU]	1.8 nF [GMC7.3183K250K3 3TR12]
1.8 nF [C0402C182K5RACT U]	1.8 nF [C0805C182K5RACT U]	1.8 nF [C1812C182KBGAC TU]	1.8 nF [MMC5.7182K100J 31TR12]
1.8 nF [C0603C182K1HACT U]	1.8 nF [C0805C182KARACT U]	1.8 nF [C1825C182KBGAC TU]	1.8 nF [MMC5.7182K250J 31TR12]
1.8 nF [C0603C182K1RACT U]			

Multisim 14.1 Education Components

1.8 nF [MMC5.7182K50J3 1TR12]	1.8 Ohm [CRL0805- JW-1R80ELF]	1.8 uF [C0805C185K8PACT U]	1.8 uF [C2220C185K5RACT U]
1.8 nF [MMC7.3182K100K 31TR12]	1.8 Ohm [CRL1206- FW-1R80ELF]	1.8 uF [C0805C185K8RACT U]	1.8 uF [C2225C185K5RACT U]
1.8 nF [MMC7.3182K250K 31TR12]	1.8 Ohm [CRL2010- FW-1R80ELF]	1.8 uF [C0805C185K9PACT U]	1.8 uF [C2225C185M5UAC TU]
1.8 nF [MMC7.3182K400K 31TR12]	1.8 Ohm [CRL2010- JW-1R80ELF]	1.8 uF [C0805C185K9RACT U]	1.8 uF [MDC10185K100A5 2P3TUBE]
1.8 nF [MMC7.3182K50K3 1TR12]	1.8 Ohm [CRL2512- FW-1R80ELF]	1.8 uF [C1206C185K3PACT U]	1.8 uF [MDC10185K50A52 P3TUBE]
1.8 nF [MMC7.3182K63K3 1TR12]	1.8 Ohm [CRM1206-FX- 1R80ELF]	1.8 uF [C1206C185K4RACT U]	1.8 uF [MDC15185K100B5 3P3TUBE]
1.8 Ohm [CR0402- J/-1R8GLF]	1.8 Ohm [CRM2512-JW- 1R8ELF]	1.8 uF [C1206C185K8RACT U]	1.8 uF [MDC15185K50B53 P3TUBE]
1.8 Ohm [CR0603- J/-1R8ELF]	1.8 Ohm [PWR2615W1R80J]	1.8 uF [C1210C185K3PACT U]	1.8 uF [MDK15185K100B5 3P3TUBE]
1.8 Ohm [CR0805- J/-1R8ELF]	1.8 Ohm [PWR263S-35- 1R80J]	1.8 uF [C1210C185K3RACT U]	1.8 uF [MDK15185K50B53 P3TUBE]
1.8 Ohm [CR1206- J/-1R8ELF]	1.8 Ohm [PWR5322W1R80JE]	1.8 uF [C1210C185K4RACT U]	1.8 uF [MMC12.7185K63B 31TR24]
1.8 Ohm [CRL0603- FW-1R80ELF]	1.8 uF [C0805C185K4PACT U]	1.8 uF [C1825C185K5RACT U]	1.8 uH [SDR0302- 1R8ML]
1.8 Ohm [CRL0603- JW-1R80ELF]	1.8 uF [C0805C185K4RACT U]		1.8 uH [SDR0403- 1R8ML]

Multisim 14.1 Education Components

1.8 uH [SDR0703-1R8ML]	1.82 kOhm [CR0402-FX-1821GLF]	1.9 kOhm [4416P-2-192]	1.96 kOhm [CRT0603-CY-1961ELF]
1.8 uH [SRN6045-1R8Y]	1.82 kOhm [CR0603-FX-1821ELF]	1.9 kOhm [4420P-1-192]	1_AMP
1.8 uH [SRP1235-1R8M]	1.82 kOhm [CR0805-FX-1821ELF]	1.91 kOhm [CR0402-FX-1911GLF]	10 kOhm [4108R-1-103]
1.8 uH [SRP1250-1R8M]	1.82 kOhm [CR1206-FX-1821ELF]	1.91 kOhm [CR0603-FX-1911ELF]	10 kOhm [4108R-1-103LF]
1.8 uH [SRP1270-1R8M]	1.82 kOhm [CR2512-FX-1821ELF]	1.91 kOhm [CR0805-FX-1911ELF]	10 kOhm [4108R-2-103]
1.8 uH [SRP7028A-1R8M]	1.82 kOhm [CR2512-FX-1821ELF]	1.91 kOhm [CR1206-FX-1911ELF]	10 kOhm [4108R-2-103LF]
1.8 uH [SRP7050TA-1R8M]	1.82 Ohm [PWR163S-25-1R82FE]	1.91 kOhm [CRM2512-FX-1911ELF]	10 kOhm [4114R-1-103]
1.8 uH [SRR1003-1R8M]	1.87 kOhm [CR0402-FX-1871GLF]	1.91 kOhm [CRM2512-FX-1911ELF]	10 kOhm [4114R-1-103LF]
1.8 uH [SRR1210-1R8Y]	1.87 kOhm [CR0603-FX-1871ELF]	1.96 kOhm [CAT16-1961F4LF]	10 kOhm [4114R-2-103]
1.8 uH [SRR1210A-1R8Y]	1.87 kOhm [CR0805-FX-1871ELF]	1.96 kOhm [CR0402-FX-1961GLF]	10 kOhm [4114R-2-103LF]
1.8 uH [SRR4018-1R8Y]	1.87 kOhm [CR1206-FX-1871ELF]	1.96 kOhm [CR0603-FX-1961ELF]	10 kOhm [4116R-1-103]
1.8 uH [SRR4028-1R8Y]	1.87 kOhm [CR1206-FX-1871ELF]	1.96 kOhm [CR0805-FX-1961ELF]	10 kOhm [4116R-1-103LF]
1.8 uH [SRR5018-1R8Y]	1.87 kOhm [CRT1206-FZ-1871ELF]	1.96 kOhm [CR1206-FX-1961ELF]	10 kOhm [4116R-2-103]
1.8 uH [SRU5016-1R8Y]			10 kOhm [4116R-2-103LF]
1.8 uH [SRU6018-1R8Y]			10 kOhm [4304M-101-103]

Multisim 14.1 Education Components

10 kOhm [4304M-101-103LF]	10 kOhm [4308H-102-103]	10 kOhm [4310H-102-103LF]	10 kOhm [4416P-T01-103]
10 kOhm [4304M-102-103]	10 kOhm [4308H-102-103LF]	10 kOhm [4310M-101-103]	10 kOhm [4416P-T02-103]
10 kOhm [4304M-102-103LF]	10 kOhm [4308M-101-103]	10 kOhm [4310M-101-103LF]	10 kOhm [4416P-T02-103LF]
10 kOhm [4306H-101-103]	10 kOhm [4308M-101-103LF]	10 kOhm [4310M-102-103]	10 kOhm [4420P-1-103]
10 kOhm [4306H-101-103LF]	10 kOhm [4308M-102-103]	10 kOhm [4310M-102-103LF]	10 kOhm [4420P-1-103LF]
10 kOhm [4306M-101-103]	10 kOhm [4308M-102-103LF]	10 kOhm [4310R-101-103]	10 kOhm [4420P-2-103]
10 kOhm [4306M-101-103LF]	10 kOhm [4308R-101-103]	10 kOhm [4310R-101-103LF]	10 kOhm [4420P-2-103LF]
10 kOhm [4306M-102-103]	10 kOhm [4308R-101-103LF]	10 kOhm [4310R-102-103]	10 kOhm [4420P-T01-103]
10 kOhm [4306M-102-103LF]	10 kOhm [4308R-102-103]	10 kOhm [4310R-102-103LF]	10 kOhm [4420P-T02-103]
10 kOhm [4306R-101-103]	10 kOhm [4308R-102-103LF]	10 kOhm [4311R-101-103]	10 kOhm [4420P-T02-103LF]
10 kOhm [4306R-101-103LF]	10 kOhm [4309R-101-103]	10 kOhm [4311R-101-103LF]	10 kOhm [4420P-T04-103]
10 kOhm [4306R-102-103]	10 kOhm [4309R-101-103LF]	10 kOhm [4416P-1-103]	10 kOhm [4604H-101-103LF]
10 kOhm [4306R-102-103LF]	10 kOhm [4310H-101-103]	10 kOhm [4416P-1-103LF]	10 kOhm [4604X-101-103LF]
10 kOhm [4308H-101-103]	10 kOhm [4310H-101-103LF]	10 kOhm [4416P-2-103]	10 kOhm [4604X-102-103LF]
10 kOhm [4308H-101-103LF]	10 kOhm [4310H-102-103]	10 kOhm [4416P-2-103LF]	10 kOhm [4604X-AP1-103LF]

Multisim 14.1 Education Components

10 kOhm [4605H-101-103LF]	10 kOhm [4608H-102-103LF]	10 kOhm [4610X-101-103LF]	10 kOhm [4814P-2-103LF]
10 kOhm [4605M-101-103LF]	10 kOhm [4608M-101-103LF]	10 kOhm [4610X-102-103LF]	10 kOhm [4814P-T01-103]
10 kOhm [4605X-101-103LF]	10 kOhm [4608M-102-103LF]	10 kOhm [4610X-AP1-103LF]	10 kOhm [4814P-T01-103LF]
10 kOhm [4605X-AP1-103LF]	10 kOhm [4608X-101-103LF]	10 kOhm [4610X-AP2-103LF]	10 kOhm [4814P-T02-103]
10 kOhm [4606H-101-103LF]	10 kOhm [4608X-102-103LF]	10 kOhm [4611M-101-103LF]	10 kOhm [4814P-T02-103LF]
10 kOhm [4606H-102-103LF]	10 kOhm [4608X-AP1-103LF]	10 kOhm [4611X-101-103LF]	10 kOhm [4816P-1-103]
10 kOhm [4606M-101-103LF]	10 kOhm [4608X-AP2-103LF]	10 kOhm [4612H-101-103LF]	10 kOhm [4816P-1-103DLF]
10 kOhm [4606M-102-103LF]	10 kOhm [4609H-101-103LF]	10 kOhm [4612X-101-103LF]	10 kOhm [4816P-1-103F]
10 kOhm [4606X-101-103LF]	10 kOhm [4609M-101-103LF]	10 kOhm [4612X-102-103LF]	10 kOhm [4816P-1-103LF]
10 kOhm [4606X-102-103LF]	10 kOhm [4609X-101-103LF]	10 kOhm [4613X-101-103LF]	10 kOhm [4816P-2-103]
10 kOhm [4606X-AP1-103LF]	10 kOhm [4609X-AP1-103LF]	10 kOhm [4614X-101-103LF]	10 kOhm [4816P-2-103F]
10 kOhm [4606X-AP2-103LF]	10 kOhm [4610H-101-103LF]	10 kOhm [4614X-102-103LF]	10 kOhm [4816P-2-103LF]
10 kOhm [4607M-101-103LF]	10 kOhm [4610H-102-103LF]	10 kOhm [4814P-1-103]	10 kOhm [4816P-4-103]
10 kOhm [4607X-101-103LF]	10 kOhm [4610M-101-103LF]	10 kOhm [4814P-1-103LF]	10 kOhm [4816P-T01-103]
10 kOhm [4608H-101-103LF]	10 kOhm [4610M-102-103LF]	10 kOhm [4814P-2-103]	10 kOhm [4816P-T01-103LF]

Multisim 14.1 Education Components

10 kOhm [4816P-T02-103]	10 kOhm [4820P-T02-103]	10 kOhm [CAY16-103J4LF]	10 kOhm [CR0805-JW-103GLF]
10 kOhm [4816P-T02-103LF]	10 kOhm [4820P-T02-103LF]	10 kOhm [CAY16-103J8LF]	10 kOhm [CR1206-FX-1002ELF]
10 kOhm [4818P-1-103]	10 kOhm [CAT10-103J4LF]	10 kOhm [CAY17-103JALF]	10 kOhm [CR1206-JW-103ELF]
10 kOhm [4818P-2-103]	10 kOhm [CAT16-1002F4LF]	10 kOhm [CR0201-FW-1002GLF]	10 kOhm [CR1206-JW-103GLF]
10 kOhm [4818P-2-103LF]	10 kOhm [CAT16-1002F8LF]	10 kOhm [CR0201-JW-103GLF]	10 kOhm [CR2010-FX-1002ELF]
10 kOhm [4818P-T01-103]	10 kOhm [CAT16-103J2LF]	10 kOhm [CR0402-FX-1002GLF]	10 kOhm [CR2010-JW-103ELF]
10 kOhm [4818P-T02-103]	10 kOhm [CAT16-103J4GLF]	10 kOhm [CR0402-JW-103GLF]	10 kOhm [CR2512-FX-1002ELF]
10 kOhm [4820P-1-103]	10 kOhm [CAT16-103J4LF]	10 kOhm [CR0603-FX-1002ELF]	10 kOhm [CR2512-JW-103ELF]
10 kOhm [4820P-1-103F]	10 kOhm [CAT16-103J8LF]	10 kOhm [CR0603-FX-1002GLF]	10 kOhm [CRM1206-FX-1002ELF]
10 kOhm [4820P-1-103LF]	10 kOhm [CAT25-103JALF]	10 kOhm [CR0603-FX-1002HLF]	10 kOhm [CRM1206-JW-103ELF]
10 kOhm [4820P-2-103]	10 kOhm [CAY10-103J2LF]	10 kOhm [CR0603-JW-103ELF]	10 kOhm [CRM2010-FX-1002ELF]
10 kOhm [4820P-2-103F]	10 kOhm [CAY10-103J4LF]	10 kOhm [CR0603-JW-103GLF]	10 kOhm [CRM2512-FX-1002ELF]
10 kOhm [4820P-2-103LF]	10 kOhm [CAY16-1002F4LF]	10 kOhm [CR0805-FX-1002ELF]	10 kOhm [CRM2512-JW-103ELF]
10 kOhm [4820P-T01-103]	10 kOhm [CAY16-103J2LF]	10 kOhm [CR0805-FX-1002GLF]	
10 kOhm [4820P-T01-103LF]	10 kOhm [CAY16-103J4GLF]	10 kOhm [CR0805-JW-103ELF]	

Multisim 14.1 Education Components

10 kOhm [CRS0805-FX- 1002ELF]	10 kOhm [CRT0603-BY- 1002ELF]	10 kOhm [CRT0805-BY- 1002ELF]	10 kOhm [PWR163S-25- 1002F]
10 kOhm [CRS1206-FX- 1002ELF]	10 kOhm [CRT0603-DY- 1002ELF]	10 kOhm [CRT0805-DY- 1002ELF]	10 kOhm [PWR163S-25- 1002J]
10 kOhm [CRS1206-JX- 103ELF]	10 kOhm [CRT0603-DZ- 1002ELF]	10 kOhm [CRT0805-DZ- 1002ELF]	10 kOhm [PWR220T-20- 1002F]
10 kOhm [CRS2512-FX- 1002ELF]	10 kOhm [CRT0603-FX- 1002ELF]	10 kOhm [CRT0805-FV- 1002ELF]	10 kOhm [PWR220T-20- 1002J]
10 kOhm [CRT0402-BW- 1002GLF]	10 kOhm [CRT0603-FY- 1002ELF]	10 kOhm [CRT0805-FX- 1002ELF]	10 kOhm [PWR220T-35- 1002F]
10 kOhm [CRT0402-BY- 1002GLF]	10 kOhm [CRT0603-FZ- 1002ELF]	10 kOhm [CRT0805-FZ- 1002ELF]	10 kOhm [PWR220T-35- 1002J]
10 kOhm [CRT0402-BZ- 1002GAS]	10 kOhm [CRT0603-PV- 1002ELF]	10 kOhm [CRT1206-AV- 1002ELF]	10 kOhm [PWR221T-30- 1002F]
10 kOhm [CRT0402-FZ- 1002GLF]	10 kOhm [CRT0805-BV- 1002ELF]	10 kOhm [CRT1206-BW- 1002ELF]	10 kOhm [PWR221T-30- 1002J]
10 kOhm [CRT0603-BV- 1002ELF]	10 kOhm [CRT0805-BW- 1002ELF]	10 kOhm [CRT1206-BY- 1002ELF]	10 kOhm [PWR263S-20- 1002F]
10 kOhm [CRT0603-BW- 1002ELF]	10 kOhm [CRT0805-BX- 1002ELF]	10 kOhm [CRT1206-FZ- 1002ELF]	10 kOhm [PWR263S-20- 1002FE]
10 kOhm [CRT0603-BY- 1002EAS]	10 kOhm [CRT0805-BY- 1002EAS]	10 kOhm [CRT1206-PV- 1002ELF]	10 kOhm [PWR263S-20- 1002J]

Multisim 14.1 Education Components

10 kOhm [PWR263S-35-1002F]	10 MOhm [4308R-102-106LF]	10 MOhm [CHV1206-JW-106ELF]	10 MOhm [CR1206-JW-106ELF]
10 kOhm [PWR263S-35-1002J]	10 MOhm [4309R-101-106LF]	10 MOhm [CHV2010-FX-1005ELF]	10 MOhm [CR1206-JW-106GLF]
10 kOhm [PWR4525W1002J]	10 MOhm [4606X-101-106LF]	10 MOhm [CHV2512-FX-1005ELF]	10 MOhm [CR2010-JW-106ELF]
10 kOhm [PWR4525W1002JE]	10 MOhm [4608X-102-106LF]	10 MOhm [CHV2512-JW-106ELF]	10 MOhm [CR2512-JW-106ELF]
10 mH [SDR0503-103JL]	10 MOhm [4609X-101-106LF]	10 MOhm [CR0201-JW-106GLF]	10 mOhm [CRA2512-FZ-R010ELF]
10 mH [SDR0906-103KL]	10 MOhm [4610X-101-106LF]	10 MOhm [CR0402-JW-106GLF]	10 mOhm [CRA2512-JZ-R010ELF]
10 mH [SDR1005-103KL]	10 MOhm [4610X-102-106LF]	10 MOhm [CR0603-FW-1005ELF]	10 mOhm [CRF0805-FX-R010ELF]
10 mH [SRE6603-103M]	10 MOhm [4816P-T01-106]	10 MOhm [CR0603-JW-106ELF]	10 mOhm [CRF1206-FX-R010ELF]
10 mH [SRR0906-103YL]	10 MOhm [4816P-T01-106LF]	10 MOhm [CR0805-FW-1005ELF]	10 mOhm [CRF2512-FX-R010ELF]
10 mH [SRR0908-103YL]	10 MOhm [CHV0603-JW-106ELF]	10 MOhm [CR0805-JW-106ELF]	10 mOhm [CRF2512-JX-R010ELF]
10 mH [SRR1208-103KL]	10 MOhm [CHV0805-FX-1005ELF]	10 MOhm [CR0805-JW-106ELF]	10 mOhm [CRL2512-FU-R010ELF]
10 mH [SRR6603-103ML]	10 MOhm [CHV0805-FX-1005ELF]	10 MOhm [CHV1206-FX-1005ELF]	
10 MOhm [4306R-101-106]	10 MOhm [CHV1206-FX-1005ELF]		
10 MOhm [4308R-102-106]	10 MOhm [CHV1206-FX-1005ELF]		

Multisim 14.1 Education Components

10 mOhm [CRL2512-JU- R010ELF]	10 mOhm [PWR4412- 2SCR0100J]	10 nF [05085C103KAT2V]	10 nF [C0402C103K4RACT U]
10 mOhm [PWR1913WR010F]	10 mOhm [PWR4412- 2SDR0100F]	10 nF [05086C103KAT2S]	10 nF [C0402C103K5RACT U]
10 mOhm [PWR1913WR010F E]	10 mOhm [PWR4412- 2SDR0100J]	10 nF [0508YC103KAT2S]	10 nF [C0402C103K8RACT U]
10 mOhm [PWR1913WR010J]	10 mOhm [PWR4525WR010J]	10 nF [06123C103KAT2S]	10 nF [C0402C103K9RACT U]
10 mOhm [PWR1913WR010JE]	10 mOhm [PWR4525WR010JE]	10 nF [06125C103KAT2V]	10 nF [C0603C103K1RACT U]
10 mOhm [PWR2615WR010F]	10 mOhm [PWR6327NR010FE]	10 nF [06126C103KAT2S]	10 nF [C0603C103K2RACT U]
10 mOhm [PWR2615WR010F E]	10 mOhm [PWR6327WR010J]	10 nF [0612ZC103KAT2S]	10 nF [C0603C103K3GACT U]
10 mOhm [PWR2615WR010J]	10 mOhm [PWR6327WR010JE]	10 nF [C0201C103K4PACT U]	10 nF [C0603C103K3HACT U]
10 mOhm [PWR2615WR010JE]	10 nF [03063C103KAT2A]	10 nF [C0201C103K8PACT U]	10 nF [C0603C103K3RACT U]
10 mOhm [PWR4412- 2SBR0100F]	10 nF [03066C103KAT2A]	10 nF [C0201C103K9PACT U]	10 nF [C0603C103K4RACT U]
10 mOhm [PWR4412- 2SBR0100J]	10 nF [0306YC103KAT2A]	10 nF [C0402C103K3RACT U]	10 nF [C0603C103K5RACT U]
10 mOhm [PWR4412- 2SCR0100F]	10 nF [0306ZC103KAT2A]		

Multisim 14.1 Education Components

10 nF [C0603C103K8RACT U]	10 nF [C0805C103K5RACT U]	10 nF [C1206C103K1RACT U]	10 nF [C1206C103M5UAC TU]
10 nF [C0603C103K9RACT U]	10 nF [C0805C103K8RACT U]	10 nF [C1206C103K2RACT U]	10 nF [C1210C103K1RACT U]
10 nF [C0805C103K1GACT U]	10 nF [C0805C103KARACT U]	10 nF [C1206C103K3GACT U]	10 nF [C1210C103K2RACT U]
10 nF [C0805C103K1HACT U]	10 nF [C0805C103M1UAC TU]	10 nF [C1206C103K3HACT U]	10 nF [C1210C103K5GACT U]
10 nF [C0805C103K1RACT U]	10 nF [C0805C103M5UAC TU]	10 nF [C1206C103K3RACT U]	10 nF [C1210C103K5RACT U]
10 nF [C0805C103K3GACT U]	10 nF [C0805F103K1RACT U]	10 nF [C1206C103K4GACT U]	10 nF [C1210C103KARACT U]
10 nF [C0805C103K3HACT U]	10 nF [C0805F103K2RACT U]	10 nF [C1206C103K4RACT U]	10 nF [C1812C103K1GACT U]
10 nF [C0805C103K3RACT U]	10 nF [C0805F103K3RACT U]	10 nF [C1206C103K5HACT U]	10 nF [C1812C103K1RACT U]
10 nF [C0805C103K4RACT U]	10 nF [C0805F103K4RACT U]	10 nF [C1206C103K5RACT U]	10 nF [C1812C103K2RACT U]
10 nF [C0805C103K5GACT U]	10 nF [C0805F103K5RACT U]	10 nF [C1206C103KARACT U]	10 nF [C1812C103K5GACT U]
10 nF [C0805C103K5HACT U]	10 nF [C1206C103K1HACT U]	10 nF [C1206C103M1UAC TU]	10 nF [C1812C103K5RACT U]

Multisim 14.1 Education Components

10 nF [C1825C103K1GACT U]	10 nF [GMC5.7102K250J3 1TR12]	10 nF [LD175C103KAB2V]	10 nF [PG124W103MAB2 S1]
10 nF [C1825C103K2GACT U]	10 nF [GMC5.7103K100J3 1TR12]	10 nF [LD17YC103KAB2S]	10 nF [PG124Z103MAB2S 1]
10 nF [C1825C103K5GACT U]	10 nF [GMC5.7103K50J31 TR12]	10 nF [LDEPD2100KA5N0 0]	10 nF [PG126D103MAB2S 1]
10 nF [C2220C103K1GACT U]	10 nF [GMC7.3102K250K3 1TR12]	10 nF [LG126Z103MAT2S 1]	10 nF [PG126W103MAB2 S1]
10 nF [C2220C103K2GACT U]	10 nF [GMC7.3103K100K3 1TR12]	10 nF [LG226C103MAT2S 1]	10 nF [PG126Z103MAB2S 1]
10 nF [C2225C103K2GACT U]	10 nF [GMC7.3103K400K3 5TR12]	10 nF [MMC5.7103K250J 31TR12]	10 nF [PG224C103MAB2S 1]
10 nF [C2225C103KCGAC TU]	10 nF [GMC7.3104K100K3 7TR12]	10 nF [MMC5.7103K50J3 1TR12]	10 nF [PG224D103MAB2S 1]
10 nF [CA064C103K3RACT U]	10 nF [GPC7.3103K63K31 TR12]	10 nF [MMC7.3103K250K 31TR12]	10 nF [PG224W103MAB2 S1]
10 nF [CA064C103K4RACT U]	10 nF [LD163C103KAB2A]	10 nF [MMC7.3103K400K 35TR12]	10 nF [PG224Z103MAB2S 1]
10 nF [CA064C103K5RACT U]	10 nF [LD166C103KAB2A]	10 nF [MMC7.3103K50K3 1TR12]	10 nF [PG226C103MAB2S 1]
10 nF [CA064C103K8RACT U]	10 nF [LD16ZC103KAB2A]	10 nF [MMC7.3103K63K3 1TR12]	10 nF [PG226D103MAB2S 1]
	10 nF [LD173C103KAB2S]	10 nF [PG124D103MAB2S 1]	

Multisim 14.1 Education Components

10 nF [PG226W103MAB2 S1]	10 Ohm [4114R-1- 100]	10 Ohm [4308R- 102-100LF]	10 Ohm [4605X- 101-100LF]
10 nF [PG226Z103MAB2S 1]	10 Ohm [4114R-1- 100LF]	10 Ohm [4309R- 101-100LF]	10 Ohm [4606X- 101-100LF]
10 nF [PG22ZC103MAB2S 1]	10 Ohm [4114R-2- 100]	10 Ohm [4310M- 102-100LF]	10 Ohm [4606X- 102-100LF]
10 nF [SPC10.2103K100A 31TR16]	10 Ohm [4114R-2- 100LF]	10 Ohm [4310R- 101-100]	10 Ohm [4606X- AP2-100LF]
10 nF [SPC10.2103K250A 31TR16]	10 Ohm [4116R-1- 100]	10 Ohm [4310R- 101-100LF]	10 Ohm [4608H- 102-100LF]
10 nF [SPC10.2103K250A 31TR16]	10 Ohm [4116R-1- 100LF]	10 Ohm [4310R- 102-100]	10 Ohm [4608X- 101-100LF]
10 nF [SPC10.2103K400A 31TR16]	10 Ohm [4116R-2- 100]	10 Ohm [4310R- 102-100LF]	10 Ohm [4608X- 102-100LF]
10 nF [SPC10.2103K400A 31TR16]	10 Ohm [4306R- 101-100]	10 Ohm [4416P-1- 100]	10 Ohm [4608X- AP2-100LF]
10 nF [SPC10.2103K630A 31TR16]	10 Ohm [4306R- 101-100LF]	10 Ohm [4416P-1- 100LF]	10 Ohm [4609X- 101-100LF]
10 nF [SPC10.2103K630A 31TR16]	10 Ohm [4306R- 102-100]	10 Ohm [4416P-2- 100]	10 Ohm [4610X- 101-100LF]
10 nF [SPC7.3103K100K31 TR12]	10 Ohm [4306R- 102-100LF]	10 Ohm [4416P- T01-100]	10 Ohm [4610X- 102-100LF]
10 nF [SPC7.3103K250K35 TR12]	10 Ohm [4308H- 102-100]	10 Ohm [4420P-1- 100]	10 Ohm [4610X- AP2-100LF]
10 nF [W2F15C1038AT1A]	10 Ohm [4308R- 101-100]	10 Ohm [4420P-1- 100LF]	10 Ohm [4611X- 101-100LF]
10 nF [W2F15C1038AT1A]	10 Ohm [4308R- 101-100LF]	10 Ohm [4420P- T01-100]	10 Ohm [4612X- 102-100LF]
10 nF [W3F15C1038AT1A]	10 Ohm [4308R- 102-100]	10 Ohm [4604X- 102-100LF]	10 Ohm [4814P-1- 100]

Multisim 14.1 Education Components

10 Ohm [4814P-1-100LF]	10 Ohm [CAT10-100J4LF]	10 Ohm [CAY17-100JALF]	10 Ohm [CR2010-FX-10R0ELF]
10 Ohm [4814P-T01-100]	10 Ohm [CAT16-100J2GLF]	10 Ohm [CR0201-JW-100GLF]	10 Ohm [CR2010-JW-100ELF]
10 Ohm [4814P-T01-100LF]	10 Ohm [CAT16-100J2LF]	10 Ohm [CR0402-FX-10R0GLF]	10 Ohm [CR2512-FX-10R0ELF]
10 Ohm [4816P-1-100]	10 Ohm [CAT16-100J4GLF]	10 Ohm [CR0402-JW-100GLF]	10 Ohm [CR2512-JW-100ELF]
10 Ohm [4816P-1-100F]	10 Ohm [CAT16-100J4LF]	10 Ohm [CR0603-FX-10R0ELF]	10 Ohm [CRM0805-JW-100ELF]
10 Ohm [4816P-1-100LF]	10 Ohm [CAT16-100J8LF]	10 Ohm [CR0603-FX-10R0GLF]	10 Ohm [CRM1206-FX-10R0ELF]
10 Ohm [4816P-2-100]	10 Ohm [CAT16-10R0F4LF]	10 Ohm [CR0603-JW-100ELF]	10 Ohm [CRM1206-JW-100ELF]
10 Ohm [4816P-2-100LF]	10 Ohm [CAT25-100JALF]	10 Ohm [CR0603-JW-100GLF]	10 Ohm [CRM2010-FX-10R0ELF]
10 Ohm [4816P-T01-100]	10 Ohm [CAY10-100J2LF]	10 Ohm [CR0805-FX-10R0ELF]	10 Ohm [CRM2512-FX-10R0ELF]
10 Ohm [4816P-T01-100LF]	10 Ohm [CAY10-100J4LF]	10 Ohm [CR0805-FX-10R0GLF]	10 Ohm [CRM2512-JW-100ELF]
10 Ohm [4816P-T02-100]	10 Ohm [CAY16-100J2LF]	10 Ohm [CR0805-JW-100ELF]	10 Ohm [CRS0805-FX-10R0ELF]
10 Ohm [4816P-T02-100LF]	10 Ohm [CAY16-100J4GLF]	10 Ohm [CR0805-JW-100GLF]	10 Ohm [CRS0805-JX-100ELF]
10 Ohm [4820P-1-100]	10 Ohm [CAY16-100J4LF]	10 Ohm [CR1206-FX-10R0ELF]	10 Ohm [CRS1206-JX-100ELF]
10 Ohm [4820P-1-100LF]	10 Ohm [CAY16-100J8LF]	10 Ohm [CR1206-JW-100ELF]	
10 Ohm [4820P-T01-100]	10 Ohm [CAY16-10R0F4LF]	10 Ohm [CR1206-JW-100GLF]	

Multisim 14.1 Education Components

10 Ohm [CRS2010-FX-10R0ELF]	10 Ohm [FW10A10R0JA]	10 Ohm [PWR220T-20-10R0J]	10 Ohm [PWR263S-35-10R0F]
10 Ohm [CRS2010-JX-100ELF]	10 Ohm [FW20A10R0JA]	10 Ohm [PWR220T-35-10R0F]	10 Ohm [PWR263S-35-10R0FE]
10 Ohm [CRS2512-FX-10R0ELF]	10 Ohm [FW30A10R0JA]	10 Ohm [PWR220T-35-10R0J]	10 Ohm [PWR263S-35-10R0J]
10 Ohm [CRS2512-JX-100ELF]	10 Ohm [FW50A10R0JA]	10 Ohm [PWR221T-30-10R0F]	10 Ohm [PWR3014W10R0JE]
10 Ohm [CRT0402-BY-10R0GLF]	10 Ohm [FW70A10R0JA]	10 Ohm [PWR221T-30-10R0J]	10 Ohm [PWR4318W10R0JE]
10 Ohm [CRT0402-FZ-10R0GLF]	10 Ohm [PWR163S-25-10R0F]	10 Ohm [PWR221T-50-10R0F]	10 Ohm [PWR4525W10R0F]
10 Ohm [CRT0603-BY-10R0ELF]	10 Ohm [PWR163S-25-10R0FE]	10 Ohm [PWR2615W10R0F]	10 Ohm [PWR4525W10R0J]
10 Ohm [CRT0603-FY-10R0ELF]	10 Ohm [PWR163S-25-10R0J]	10 Ohm [PWR2615W10R0J]	10 Ohm [PWR4525W10R0JE]
10 Ohm [CRT0603-FZ-10R0ELF]	10 Ohm [PWR163S-25-10R0JE]	10 Ohm [PWR2615W10R0JE]	10 Ohm [PWR5322W10R0JE]
10 Ohm [CRT0805-BW-10R0ELF]	10 Ohm [PWR1913W10R0J]	10 Ohm [PWR263S-20-10R0F]	10 Ohm [PWR6327W10R0J]
10 Ohm [CRT0805-BY-10R0ELF]	10 Ohm [PWR1913W10R0JE]	10 Ohm [PWR263S-20-10R0FE]	10 Ohm [PWR6327W10R0JE]
10 Ohm [CRT0805-CX-10R0ELF]	10 Ohm [PWR2010W10R0JE]	10 Ohm [PWR263S-20-10R0J]	10 pF [C0402C100K3GACTU]
10 Ohm [CRT0805-CY-10R0ELF]	10 Ohm [PWR220T-20-10R0F]		
10 Ohm [CRT1206-BY-10R0ELF]			
10 Ohm [CRT1206-DW-10R0ELF]			

Multisim 14.1 Education Components

10 pF [C0402C100K4GACT U]	10 pF [C0805C100KDGAC TU]	10 pF [C2220C100KBGAC TU]	10 uF [C0805C106K8PACT U]
10 pF [C0402C100K5GACT U]	10 pF [C0805H100K5GAC TU]	10 pF [C2225C100KBGAC TU]	10 uF [C0805C106K9PACT U]
10 pF [C0402C100K8GACT U]	10 pF [C1206C100K1GACT U]	10 pF [CA064C100K1GAC TU]	10 uF [C0805C106M9VAC TU]
10 pF [C0603C100K1GACT U]	10 pF [C1206C100K2GACT U]	10 pF [CA064C100K2GAC TU]	10 uF [C1206C106K3PACT U]
10 pF [C0603C100K2GACT U]	10 pF [C1206C100K5GACT U]	10 pF [CA064C100K4GAC TU]	10 uF [C1206C106K4PACT U]
10 pF [C0603C100K3GACT U]	10 pF [C1206C100KBGAC TU]	10 pF [CA064C100K5GAC TU]	10 uF [C1206C106K4RACT U]
10 pF [C0603C100K5GACT U]	10 pF [C1210C100K2GACT U]	10 uF [12TPC10M] 10 uF [16TQC10M]	10 uF [C1206C106K8PACT U]
10 pF [C0805C100K1GACT U]	10 pF [C1210C100K5GACT U]	10 uF [35TQC10M] 10 uF [6TPU10MSI]	10 uF [C1206C106K8RACT U]
10 pF [C0805C100K2GACT U]	10 pF [C1210C100KBGAC TU]	10 uF [A700V106M016AT E045]	10 uF [C1206C106K9PACT U]
10 pF [C0805C100K5GACT U]	10 pF [C1812C100KBGAC TU]	10 uF [A700V106M12RAT E060]	10 uF [C1206C106K9RACT U]
10 pF [C0805C100KBGAC TU]	10 pF [C1825C100KBGAC TU]	10 uF [C0805C106K4PACT U]	10 uF [C1206C106M8VAC TU]

Multisim 14.1 Education Components

10 uF [C1206C106M9VAC TU]	10 uF [C1210C106M8VAC TU]	10 uF [NOJA106K006RWJ]	10 uF [T491C106M010AT]
10 uF [C1210C106K3PACT U]	10 uF [C1210C106M9VAC TU]	10 uF [NOSA106K006R20 00]	10 uF [T491C106M016AT]
10 uF [C1210C106K3RACT U]	10 uF [EEFCS1D100R]	10 uF [T429E106M020AH 4250]	10 uF [T491C106M020AT]
10 uF [C1210C106K4PACT U]	10 uF [EEFCS1E100R]	10 uF [T429H106M035AH 4250]	10 uF [T491C106M025AT]
10 uF [C1210C106K4RACT U]	10 uF [EEFCS1V100R]	10 uF [T491A106M004AT]	10 uF [T491D106M025AT]
10 uF [C1210C106K8NAC TU]	10 uF [EEHZA1H100R]	10 uF [T491A106M006AT]	10 uF [T491D106M035AT]
10 uF [C1210C106K8PACT U]	10 uF [EEHZA1J100P]	10 uF [T491A106M010AT]	10 uF [T491D106M050AT]
10 uF [C1210C106K8RACT U]	10 uF [EEHZC1H100R]	10 uF [T491A106M016AT]	10 uF [T491S106M004AT]
10 uF [C1210C106K8PACT U]	10 uF [EEHZC1J100P]	10 uF [T491A106M020AT]	10 uF [T491S106M006AT]
10 uF [C1210C106K8RACT U]	10 uF [MDC10106K100A5 8P7TUBE]	10 uF [T491B106M004AT]	10 uF [T491S106M010AT]
10 uF [C1210C106K9PACT U]	10 uF [MDC10106K100A5 8P8TUBE]	10 uF [T491B106M006AT]	10 uF [T491T106M006AT]
10 uF [C1210C106K9RACT U]	10 uF [MDC10106K50A57 P7TUBE]	10 uF [T491B106M010AT]	10 uF [T491T106M010AT]
10 uF [C1210C106M4VAC TU]	10 uF [MDC10106K50A57 P8TUBE]	10 uF [T491B106M016AT]	10 uF [T491T106M016AT]

Multisim 14.1 Education Components

10 uF [T491U106M016AT]	10 uF [T494B106M020AT]	10 uF [T494T106M016AT]	10 uF [T495D106M035AT E125]
10 uF [T491U106M020AT]	10 uF [T494C106M010AT]	10 uF [T494U106M016AT]	10 uF [T495D106M035AT E250]
10 uF [T491V106M035AT]	10 uF [T494C106M016AT]	10 uF [T494U106M020AT]	10 uF [T495D106M035AT E300]
10 uF [T491X106M050AT]	10 uF [T494C106M025AT]	10 uF [T494V106M035AT]	10 uF [T495T106M016AT E4K0]
10 uF [T493C106M020AH 6110]	10 uF [T494C106M035AT]	10 uF [T494X106M050AT]	10 uF [T495X106M035AT E200]
10 uF [T494A106M004AT]	10 uF [T494D106M025AT]	10 uF [T495A106M010AT E1K8]	10 uF [T495X106M035AT E250]
10 uF [T494A106M006AT]	10 uF [T494D106M035AT]	10 uF [T495B106M010AT E750]	10 uF [T495X106M050AT E250]
10 uF [T494A106M010AT]	10 uF [T494D106M050AT]	10 uF [T495B106M020AT E1K0]	10 uF [T495X106M050AT E260]
10 uF [T494A106M016AT]	10 uF [T494S106M004AT]	10 uF [T495C106M020AT E400]	10 uF [T495X106M050AT E300]
10 uF [T494B106M004AT]	10 uF [T494S106M006AT]	10 uF [T495C106M020AT E475]	10 uF [T496D106M025AT 6110]
10 uF [T494B106M006AT]	10 uF [T494S106M010AT]	10 uF [T495C106M025AT E275]	10 uF [T497F106M015AT 6110]
10 uF [T494B106M010AT]	10 uF [T494T106M006AT]	10 uF [T495C106M025AT E450]	
10 uF [T494B106M016AT]	10 uF [T494T106M010AT]		

Multisim 14.1 Education Components

10 uF [T498B106M006AT E2K1]	10 uF [T520B106M016AT E100]	10 uF [TAJA106K016RNJ]	10 uF [TAJE106K050RNJ]
10 uF [T498B106M010AT E1K8]	10 uF [T521D106M050AT E090]	10 uF [TAJB106K006RNJ]	10 uF [TAJP106K010RNJ]
10 uF [T498B106M016AT E2K8]	10 uF [T521X106M063AT E050]	10 uF [TAJB106K016RNJ]	10 uF [TAJR106K004RNJ]
10 uF [T498C106M016AT E1K4]	10 uF [T541X106M063AH 6510]	10 uF [TAJB106K020RNJ]	10 uF [TAJS106K002RNJ]
10 uF [T498C106M020AT E1K1]	10 uF [TACL106K002RTA]	10 uF [TAJB106K025RNJ]	10 uF [TAJS106K004RNJ]
10 uF [T498C106M025AT E1K1]	10 uF [TACL106K003RTA]	10 uF [TAJC106K016RNJ]	10 uF [TAJS106K010RNJ]
10 uF [T498D106M035AT E700]	10 uF [TACL106K006RTA]	10 uF [TAJC106K020RNJ]	10 uF [TAJT106K004RNJ]
10 uF [T498D106M050AT E1K0]	10 uF [TACR106K004RTA]	10 uF [TAJC106K025RNJ]	10 uF [TAJT106K006RNJ]
10 uF [T510X106M050AT E090]	10 uF [TACR106K006RTA]	10 uF [TAJC106K035RNJ]	10 uF [TAJT106K010RNJ]
10 uF [T510X106M050AT E120]	10 uF [TACR106K010RTA]	10 uF [TAJD106K025RNJ]	10 uF [TAJT106K016RNJ]
10 uF [T520A106M010AT E080]	10 uF [TAJA106K004RNJ]	10 uF [TAJD106K035RNJ]	10 uF [TAJW106K016RNJ]
	10 uF [TAJA106K006RNJ]	10 uF [TAJD106K050RNJ]	10 uF [TAJW106K020RNJ]
	10 uF [TAJA106K010RNJ]	10 uF [TAJE106K035RNJ]	10 uF [TAJW106K025RNJ]

Multisim 14.1 Education Components

10 uF [TAJX106K035RNJ]	10 uF [TPSB106K016R050 0]	10 uF [TPSD106K035R012 5]	10 uF [TPST106K010R100 0]
10 uF [TAJY106K035RNJ]	10 uF [TPSB106K016R080 0]	10 uF [TPSD106K035R030 0]	10 uF [TPST106K010R200 0]
10 uF [THJB106K016RJN]	10 uF [TPSB106K020R100 0]	10 uF [TPSD106K050R050 0]	10 uF [TPST106K016R080 0]
10 uF [THJD106K035RJN]	10 uF [TPSB106K025R180 0]	10 uF [TPSE106K035R020 0]	10 uF [TPST106K016R100 0]
10 uF [THJE106K050RJN]	10 uF [TPSC106K016R050 0]	10 uF [TPSE106K050R040 0]	10 uF [TPSW106K016R06 00]
10 uF [TPMD106K050R01 40]	10 uF [TPSC106K020R050 0]	10 uF [TPSE106K050R050 0]	10 uF [TRJA106K010RRJ]
10 uF [TPME106K050R01 20]	10 uF [TPSC106K020R070 0]	10 uF [TPSR106K004R300 0]	10 uF [TRJB106K010RRJ]
10 uF [TPSA106K006R150 0]	10 uF [TPSC106K025R030 0]	10 uF [TPSR106K006R100 0]	10 uF [TRJB106K016RRJ]
10 uF [TPSA106K010R090 0]	10 uF [TPSC106K025R050 0]	10 uF [TPSR106K006R150 0]	10 uF [TRJC106K020RRJ]
10 uF [TPSA106K010R180 0]	10 uF [TPSC106K035R060 0]	10 uF [TPSR106K006R300 0]	10 uF [TRJC106K025RRJ]
10 uF [TPSA106K016R100 0]	10 uF [TPSD106K025R050 0]	10 uF [TPST106K006R100 0]	10 uF [TRJD106K035RRJ]

Multisim 14.1 Education Components

10 uF [TRJE106K050RRJ]	10 uH [SDR1030- 100M]	10 uH [SRN4026- 100M]	10 uH [SRP5015TA- 100M]
10 uH [SDE0403A- 100M]	10 uH [SDR1045- 100M]	10 uH [SRN5020- 100M]	10 uH [SRP5030T- 100M]
10 uH [SDE0604A- 100M]	10 uH [SDR1105- 100ML]	10 uH [SRN5040- 100M]	10 uH [SRP5030TA- 100M]
10 uH [SDE0805A- 100M]	10 uH [SDR1305- 100M]	10 uH [SRN6028- 100M]	10 uH [SRP6540- 100M]
10 uH [SDE1006A- 100M]	10 uH [SDR1307- 100ML]	10 uH [SRN6045- 100M]	10 uH [SRP7028A- 100M]
10 uH [SDR0302- 100ML]	10 uH [SDR1307A- 100M]	10 uH [SRN8040- 100M]	10 uH [SRP7030- 100FM]
10 uH [SDR0403- 100ML]	10 uH [SDR1806- 100ML]	10 uH [SRP1038A- 100M]	10 uH [SRP7050TA- 100M]
10 uH [SDR0503- 100ML]	10 uH [SDR6603- 100M]	10 uH [SRP1040- 100M]	10 uH [SRR0603- 100ML]
10 uH [SDR0603- 100ML]	10 uH [SDR7030- 100M]	10 uH [SRP1235- 100M]	10 uH [SRR0604- 100ML]
10 uH [SDR0604- 100ML]	10 uH [SDR7045- 100M]	10 uH [SRP1245A- 100M]	10 uH [SRR0618- 100ML]
10 uH [SDR0703- 100KL]	10 uH [SRN1060- 100M]	10 uH [SRP1250- 100M]	10 uH [SRR0735A- 100M]
10 uH [SDR0805- 100ML]	10 uH [SRN3010- 100M]	10 uH [SRP1270- 100M]	10 uH [SRR0745A- 100M]
10 uH [SDR0906- 100ML]	10 uH [SRN3015- 100M]	10 uH [SRP1770TA- 100M]	10 uH [SRR0804- 100M]
10 uH [SDR1005- 100ML]	10 uH [SRN4012T- 100M]	10 uH [SRP4012TA- 100M]	10 uH [SRR0805- 100M]
10 uH [SDR1006- 100ML]	10 uH [SRN4018- 100M]	10 uH [SRP4020TA- 100M]	10 uH [SRR0905- 100M]

Multisim 14.1 Education Components

10 uH [SRR0906-100ML]	10 uH [SRR4011-100YL]	10 uH [SRU1048-100Y]	10 uH [SRU5028-100Y]
10 uH [SRR0908-100ML]	10 uH [SRR4018-100Y]	10 uH [SRU1048A-100Y]	10 uH [SRU5028A-100Y]
10 uH [SRR1003-100M]	10 uH [SRR4028-100Y]	10 uH [SRU1063-100Y]	10 uH [SRU6011-100Y]
10 uH [SRR1005-100M]	10 uH [SRR5018-100Y]	10 uH [SRU2009-100Y]	10 uH [SRU6018-100Y]
10 uH [SRR1205-100ML]	10 uH [SRR5028-100Y]	10 uH [SRU2011-100Y]	10 uH [SRU6025-100Y]
10 uH [SRR1206-100ML]	10 uH [SRR6028-100Y]	10 uH [SRU2013-100Y]	10 uH [SRU6025A-100Y]
10 uH [SRR1208-100ML]	10 uH [SRR6038-100Y]	10 uH [SRU2016-100Y]	10 uH [SRU8028-100Y]
10 uH [SRR1210-100M]	10 uH [SRR6040A-100M]	10 uH [SRU3011-100Y]	10 uH [SRU8028A-100Y]
10 uH [SRR1210A-100M]	10 uH [SRR6603-100ML]	10 uH [SRU3014-100Y]	10 uH [SRU8043-100Y]
10 uH [SRR1240-100M]	10 uH [SRR7032-100M]	10 uH [SRU3017-100Y]	10.1 kOhm [CRT1206-BY-1012ELF]
10 uH [SRR1260-100M]	10 uH [SRR7045-100M]	10 uH [SRU3028-100Y]	10.2 kOhm [CR0402-FX-1022GLF]
10 uH [SRR1260A-100M]	10 uH [SRU1028-100Y]	10 uH [SRU3028A-100Y]	10.2 kOhm [CR0603-FX-1022ELF]
10 uH [SRR1280-100M]	10 uH [SRU1028A-100Y]	10 uH [SRU5011-100Y]	10.2 kOhm [CR0805-FX-1022ELF]
10 uH [SRR1806-100M]	10 uH [SRU1038-100Y]	10 uH [SRU5016-100Y]	
10 uH [SRR3011-100YL]	10 uH [SRU1038A-100Y]	10 uH [SRU5018-100Y]	

Multisim 14.1 Education Components

10.2 kOhm [CR1206-FX-1022ELF]	10.5 Ohm [CR0805-FX-10R5ELF]	100 kOhm [4108R-1-104LF]	100 kOhm [4306M-102-104]
10.2 kOhm [CRT0402-BW-1022GLF]	10.5 Ohm [CR0805-FX-10R5GLF]	100 kOhm [4114R-1-104]	100 kOhm [4306M-102-104LF]
10.2 kOhm [CRT0805-BY-1022ELF]	10.5 Ohm [CR1206-FX-10R5ELF]	100 kOhm [4114R-1-104LF]	100 kOhm [4306R-101-104]
10.2 kOhm [CRT0805-DZ-1022ELF]	10.5 Ohm [PWR6327N10R5FE]	100 kOhm [4114R-2-104]	100 kOhm [4306R-101-104LF]
10.2 Ohm [CR0805-FX-10R2ELF]	10.7 kOhm [CR0402-FX-1072GLF]	100 kOhm [4114R-2-104LF]	100 kOhm [4306R-102-104]
10.2 Ohm [CR1206-FX-10R2ELF]	10.7 kOhm [CR0603-FX-1072ELF]	100 kOhm [4116R-1-104]	100 kOhm [4306R-102-104LF]
10.5 kOhm [CR0402-FX-1052GLF]	10.7 kOhm [CR0805-FX-1072ELF]	100 kOhm [4116R-1-104LF]	100 kOhm [4308H-101-104]
10.5 kOhm [CR0603-FX-1052ELF]	10.7 kOhm [CR1206-FX-1072ELF]	100 kOhm [4116R-2-104]	100 kOhm [4308H-102-104]
10.5 kOhm [CR0805-FX-1052ELF]	10.7 kOhm [CR0805-FX-1072ELF]	100 kOhm [4116R-2-104LF]	100 kOhm [4308H-102-104LF]
10.5 kOhm [CR1206-FX-1052ELF]	10.7 kOhm [CR1206-FX-1072ELF]	100 kOhm [4304M-101-104]	100 kOhm [4308M-102-104]
10.5 kOhm [CR0805-FX-1052ELF]	10.7 kOhm [CRT0402-BY-1072GLF]	100 kOhm [4304M-101-104LF]	100 kOhm [4308M-102-104LF]
10.5 kOhm [CR1206-FX-1052ELF]	10.7 kOhm [CRT0805-DZ-1072ELF]	100 kOhm [4304M-102-104]	100 kOhm [4308R-101-104]
10.5 kOhm [CRT0402-FZ-1052GLF]	10.7 Ohm [CR1206-FX-10R7ELF]	100 kOhm [4304M-102-104LF]	100 kOhm [4308R-101-104LF]
10.5 kOhm [CRT0805-CX-1052ELF]	10 AMP	100 kOhm [4306H-101-104]	100 kOhm [4308R-102-104]
	100 kOhm [4108R-1-104]	100 kOhm [4306H-101-104LF]	100 kOhm [4308R-102-104LF]

Multisim 14.1 Education Components

100 kOhm [4309R-101-104]	100 kOhm [4416P-1-104]	100 kOhm [4606H-101-104LF]	100 kOhm [4609M-101-104LF]
100 kOhm [4309R-101-104LF]	100 kOhm [4416P-2-104]	100 kOhm [4606H-102-104LF]	100 kOhm [4609X-101-104LF]
100 kOhm [4310H-101-104]	100 kOhm [4416P-T01-104]	100 kOhm [4606M-101-104LF]	100 kOhm [4609X-AP1-104LF]
100 kOhm [4310H-101-104LF]	100 kOhm [4416P-T02-104]	100 kOhm [4606M-102-104LF]	100 kOhm [4610H-101-104LF]
100 kOhm [4310H-102-104]	100 kOhm [4420P-1-104]	100 kOhm [4606X-101-104LF]	100 kOhm [4610M-101-104LF]
100 kOhm [4310H-102-104LF]	100 kOhm [4420P-1-104LF]	100 kOhm [4606X-102-104LF]	100 kOhm [4610M-102-104LF]
100 kOhm [4310M-101-104]	100 kOhm [4420P-2-104]	100 kOhm [4606X-AP1-104LF]	100 kOhm [4610X-101-104LF]
100 kOhm [4310M-101-104LF]	100 kOhm [4420P-2-104LF]	100 kOhm [4606X-AP2-104LF]	100 kOhm [4610X-102-104LF]
100 kOhm [4310M-102-104]	100 kOhm [4420P-T01-104]	100 kOhm [4607X-101-104LF]	100 kOhm [4610X-AP1-104LF]
100 kOhm [4310R-101-104]	100 kOhm [4420P-T02-104]	100 kOhm [4608H-102-104LF]	100 kOhm [4610X-AP2-104LF]
100 kOhm [4310R-101-104LF]	100 kOhm [4604X-101-104LF]	100 kOhm [4608M-102-104LF]	100 kOhm [4611X-101-104LF]
100 kOhm [4310R-102-104]	100 kOhm [4604X-102-104LF]	100 kOhm [4608X-101-104LF]	100 kOhm [4612X-101-104LF]
100 kOhm [4310R-102-104LF]	100 kOhm [4605H-101-104LF]	100 kOhm [4608X-102-104LF]	100 kOhm [4612X-102-104LF]
100 kOhm [4311R-101-104]	100 kOhm [4605X-101-104LF]	100 kOhm [4608X-AP1-104LF]	100 kOhm [4613X-101-104LF]
100 kOhm [4311R-101-104LF]	100 kOhm [4605X-AP1-104LF]	100 kOhm [4608X-AP2-104LF]	100 kOhm [4614X-102-104LF]

Multisim 14.1 Education Components

100 kOhm [4814P-1-104]	100 kOhm [4816P-T01-104LF]	100 kOhm [CAT10-104J4LF]	100 kOhm [CHV0603-JW-104ELF]
100 kOhm [4814P-1-104LF]	100 kOhm [4816P-T02-104]	100 kOhm [CAT16-1003F4LF]	100 kOhm [CHV0805-FX-1003ELF]
100 kOhm [4814P-2-104]	100 kOhm [4816P-T02-104LF]	100 kOhm [CAT16-1003F8LF]	100 kOhm [CHV0805-JW-104ELF]
100 kOhm [4814P-2-104LF]	100 kOhm [4818P-1-104]	100 kOhm [CAT16-104J2LF]	100 kOhm [CHV1206-FX-1003ELF]
100 kOhm [4814P-T01-104]	100 kOhm [4818P-1-104LF]	100 kOhm [CAT16-104J4LF]	100 kOhm [CHV1206-JW-104ELF]
100 kOhm [4814P-T01-104LF]	100 kOhm [4818P-2-104]	100 kOhm [CAT16-104J8LF]	100 kOhm [CHV2010-FX-1003ELF]
100 kOhm [4814P-T02-104]	100 kOhm [4818P-2-104LF]	100 kOhm [CAT25-104JALF]	100 kOhm [CHV2010-JW-104ELF]
100 kOhm [4814P-T02-104LF]	100 kOhm [4818P-T01-104]	100 kOhm [CAY10-104J2LF]	100 kOhm [CHV2010-JW-104ELF]
100 kOhm [4816P-1-104]	100 kOhm [4818P-T02-104]	100 kOhm [CAY10-104J4LF]	100 kOhm [CHV2512-FX-1003ELF]
100 kOhm [4816P-1-104DLF]	100 kOhm [4820P-1-104]	100 kOhm [CAY16-1003F4LF]	100 kOhm [CR0201-FW-1003GLF]
100 kOhm [4816P-1-104F]	100 kOhm [4820P-1-104LF]	100 kOhm [CAY16-104J2LF]	100 kOhm [CR0201-JW-104GLF]
100 kOhm [4816P-1-104LF]	100 kOhm [4820P-2-104]	100 kOhm [CAY16-104J4GLF]	100 kOhm [CR0402-FX-1003GLF]
100 kOhm [4816P-2-104]	100 kOhm [4820P-2-104LF]	100 kOhm [CAY16-104J4LF]	
100 kOhm [4816P-2-104LF]	100 kOhm [4820P-T01-104]	100 kOhm [CAY16-104J8LF]	
100 kOhm [4816P-T01-104]	100 kOhm [4820P-T02-104]	100 kOhm [CAY17-104JALF]	

Multisim 14.1 Education Components

100 kOhm [CR0402-JW-104GLF]	100 kOhm [CR1206-FX-1003GLF]	100 kOhm [CRT0402-DZ-1003GAS]	100 kOhm [CRT1206-DY-1003ELF]
100 kOhm [CR0603-FX-1003ELF]	100 kOhm [CR1206-JW-104ELF]	100 kOhm [CRT0402-FZ-1003GLF]	100 kOhm [CRT1206-FZ-1003ELF]
100 kOhm [CR0603-FX-1003GLF]	100 kOhm [CR1206-JW-104GLF]	100 kOhm [CRT0603-BY-1003ELF]	100 kOhm [CRT1206-PY-1003ELF]
100 kOhm [CR0603-FX-1003HLF]	100 kOhm [CR2010-JW-104ELF]	100 kOhm [CRT0603-FY-1003ELF]	100 kOhm [PWR220T-20-1003F]
100 kOhm [CR0603-JW-104ELF]	100 kOhm [CR2512-JW-104ELF]	100 kOhm [CRT0603-FZ-1003ELF]	100 kOhm [PWR220T-20-1003J]
100 kOhm [CR0603-JW-104GLF]	100 kOhm [CRM1206-FX-1003ELF]	100 kOhm [CRT0805-BY-1003ELF]	100 kOhm [PWR263S-20-1003F]
100 kOhm [CR0805-FX-1003ELF]	100 kOhm [CRM2010-FX-1003ELF]	100 kOhm [CRT0805-BZ-1003ELF]	100 kOhm [PWR263S-20-1003J]
100 kOhm [CR0805-FX-1003GLF]	100 kOhm [CRM2512-FX-1003ELF]	100 kOhm [CRT0805-DY-1003ELF]	100 kOhm [PWR263S-35-1003F]
100 kOhm [CR0805-JW-104ELF]	100 kOhm [CRM2512-JW-104ELF]	100 kOhm [CRT0805-DZ-1003ELF]	100 kOhm [PWR263S-35-1003J]
100 kOhm [CR0805-JW-104GLF]	100 kOhm [CRT0402-BY-1003GLF]	100 kOhm [CRT1206-BY-1003EAS]	100 MOhm [CHV2512-JW-107ELF]
100 kOhm [CR1206-FX-1003ELF]	100 kOhm [CRT0402-CZ-1003GLF]	100 kOhm [CRT1206-BY-1003ELF]	100 mOhm [CRA2512-FZ-R100ELF]

Multisim 14.1 Education Components

100 mOhm [CRA2512-JZ- R100ELF]	100 mOhm [CRM0805-FX- R100ELF]	100 mOhm [PWR1913WR100F E]	100 mOhm [PWR2615WR100J]
100 mOhm [CRL0603-FW- R100ELF]	100 mOhm [CRM0805-JX- R100ELF]	100 mOhm [PWR1913WR100J]	100 mOhm [PWR2615WR100JE]
100 mOhm [CRL0603-JW- R100ELF]	100 mOhm [CRM1206-FX- R100ELF]	100 mOhm [PWR1913WR100JE]	100 mOhm [PWR263S-35- R100F]
100 mOhm [CRL0805-FW- R100ELF]	100 mOhm [CRM2010-FX- R100ELF]	100 mOhm [PWR2010WR100F E]	100 mOhm [PWR263S-35- R100FE]
100 mOhm [CRL0805-JW- R100ELF]	100 mOhm [CRM2512-FX- R100ELF]	100 mOhm [PWR2010WR100JE]	100 mOhm [PWR3014WR100JE]
100 mOhm [CRL1206-FW- R100ELF]	100 mOhm [CRM2512-JX- R100ELF]	100 mOhm [PWR220T-20- R100F]	100 mOhm [PWR4318WR100JE]
100 mOhm [CRL1206-JW- R100ELF]	100 mOhm [PWR163S-25- R100F]	100 mOhm [PWR220T-20- R100J]	100 mOhm [PWR4412- 2SBR1000F]
100 mOhm [CRL2010-FW- R100ELF]	100 mOhm [PWR163S-25- R100FE]	100 mOhm [PWR220T-35- R100F]	100 mOhm [PWR4412- 2SBR1000J]
100 mOhm [CRL2010-JW- R100ELF]	100 mOhm [PWR163S-25- R100J]	100 mOhm [PWR221T-30- R100F]	100 mOhm [PWR4412- 2SCR1000F]
100 mOhm [CRL2512-FW- R100ELF]	100 mOhm [PWR163S-25- R100JE]	100 mOhm [PWR221T-30- R100J]	100 mOhm [PWR4412- 2SCR1000J]
100 mOhm [CRL2512-JW- R100ELF]	100 mOhm [PWR1913WR100F]	100 mOhm [PWR2615WR100F]	100 mOhm [PWR4412- 2SDR1000F]
		100 mOhm [PWR2615WR100F E]	

Multisim 14.1 Education Components

100 mOhm [PWR4412- 2SDR1000J]	100 nF [05086C104KAT2S]	100 nF [C0402C104K9PACT U]	100 nF [C0805C104K3RACT U]
100 mOhm [PWR4525WR100F]	100 nF [0508YC104KAT2V]	100 nF [C0402C104K9RACT U]	100 nF [C0805C104K4RACT U]
100 mOhm [PWR4525WR100J]	100 nF [0508ZC104KAT2S]	100 nF [C0603C104K3RACT U]	100 nF [C0805C104K5RACT U]
100 mOhm [PWR4525WR100JE]	100 nF [06123C104KAT2V]	100 nF [C0603C104K4RACT U]	100 nF [C0805C104K8RACT U]
100 mOhm [PWR5322WR100JE]	100 nF [06125C104KAT2W]	100 nF [C0603C104K5RACT U]	100 nF [C0805C104K9RACT U]
100 mOhm [PWR6327WR100F E]	100 nF [06126C104KAT2S]	100 nF [C0603C104K8RACT U]	100 nF [C0805C104M3VAC TU]
100 mOhm [PWR6327WR100J]	100 nF [0612YC104KAT2S]	100 nF [C0603C104K9RACT U]	100 nF [C0805C104M4VAC TU]
100 mOhm [PWR6327WR100JE]	100 nF [0612ZC104KAT2S]	100 nF [C0603C104M3VAC TU]	100 nF [C0805C104M5UAC TU]
100 nF [03066C104KAT2A]	100 nF [C0201C104K9PACT U]	100 nF [C0603C104M4VAC TU]	100 nF [C0805C104M5VAC TU]
100 nF [0306YD104KAT2A]	100 nF [C0402C104K4PACT U]	100 nF [C0603C104M8VAC TU]	100 nF [C1206C104K1RACT U]
100 nF [0306ZC104KAT2A]	100 nF [C0402C104K8PACT U]	100 nF [C0805C104K1RACT U]	
100 nF [05083C104KAT2A]			
100 nF [05085C104KAT2A]	100 nF [06123C104KAT2V]		

Multisim 14.1 Education Components

100 nF [C1206C104K3GACT U]	100 nF [C1206F104K4RACT U]	100 nF [C1210C104K5HACT U]	100 nF [C1812C104K1GACT U]
100 nF [C1206C104K3HACT U]	100 nF [C1206F104K5RACT U]	100 nF [C1210C104K5RACT U]	100 nF [C1812C104K1HACT U]
100 nF [C1206C104K3RACT U]	100 nF [C1210C104K1GACT U]	100 nF [C1210C104K8RACT U]	100 nF [C1812C104K1R1C7 186]
100 nF [C1206C104K4RACT U]	100 nF [C1210C104K1HACT U]	100 nF [C1210C104KARACT U]	100 nF [C1812C104K1RACT U]
100 nF [C1206C104K5RACT U]	100 nF [C1210C104K1RACT U]	100 nF [C1210C104M1UAC TU]	100 nF [C1812C104K2RACT U]
100 nF [C1206C104KARACT U]	100 nF [C1210C104K2RACT U]	100 nF [C1210C104M5UAC TU]	100 nF [C1812C104K5GACT U]
100 nF [C1206C104M1UAC TU]	100 nF [C1210C104K3GACT U]	100 nF [C1210F104K1RACT U]	100 nF [C1812C104K5HACT U]
100 nF [C1206C104M5UAC TU]	100 nF [C1210C104K3HACT U]	100 nF [C1210F104K2RACT U]	100 nF [C1812C104K5RACT U]
100 nF [C1206F104K1RACT U]	100 nF [C1210C104K3RACT U]	100 nF [C1210F104K3RACT U]	100 nF [C1812C104M1UAC TU]
100 nF [C1206F104K2RACT U]	100 nF [C1210C104K4RACT U]	100 nF [C1210F104K4RACT U]	100 nF [C1812F104K1RACT U]
100 nF [C1206F104K3RACT U]	100 nF [C1210C104K5GACT U]	100 nF [C1210F104K5RACT U]	100 nF [C1812F104K2RACT U]

Multisim 14.1 Education Components

100 nF [C1812F104K3RACT U]	100 nF [CA064C104K8RACT U]	100 nF [MDC10104K100A5 2P3TUBE]	100 nF [MDK10104K100A5 2P3TUBE]
100 nF [C1812F104K5RACT U]	100 nF [GMC5.7104K50J31 TR12]	100 nF [MDC10104K250A5 2P3TUBE]	100 nF [MDK10104K250A5 2P3TUBE]
100 nF [C1825C104K1RACT U]	100 nF [GMC7.3102K400K3 1TR12]	100 nF [MDC10104K400A5 2P3TUBE]	100 nF [MDK10104K400A5 2P3TUBE]
100 nF [C1825C104K2RACT U]	100 nF [GMC7.3104K63K31 TR12]	100 nF [MDC10104K50A52 P3TUBE]	100 nF [MDK10104K50A52 P3TUBE]
100 nF [C2220C104K1GACT U]	100 nF [GPC7.3104K63K37 TR12]	100 nF [MDC10104K630A5 8P7TUBE]	100 nF [MDK10104K630A5 8P7TUBE]
100 nF [C2220C104K2GACT U]	100 nF [LD166C104KAB2A]	100 nF [MDC10104K630A5 8P8TUBE]	100 nF [MDK10104K630A5 8P8TUBE]
100 nF [C2220C104K5GACT U]	100 nF [LD16ZC104KAB2A]	100 nF [MDC15104K100B5 3P3TUBE]	100 nF [MDK15104K250B5 3P3TUBE]
100 nF [C2225C104K1RACT U]	100 nF [LD173C104KAB2A]	100 nF [MDC15104K250B5 3P3TUBE]	100 nF [MDS10104K100A5 2P3TUBE]
100 nF [C2225C104K2RACT U]	100 nF [LD17YC104KAB2V]	100 nF [MDC15104K400B5 3P3TUBE]	100 nF [MDS10104K250A5 2P3TUBE]
100 nF [C2225C104K5RACT U]	100 nF [LD18ZC104KAB2S]	100 nF [MDC15104K50B53 P3TUBE]	100 nF [MDS10104K400A5 2P3TUBE]
100 nF [CA064C104K4RACT U]	100 nF [LG126D104MAT2S 1]	100 nF [MDC15104K630B5 3P3TUBE]	100 nF [MDS10104K50A52 P3TUBE]

Multisim 14.1 Education Components

100 nF [MDS15104K100B5 3P3TUBE]	100 nF [PG224W104MAB2 S1]	100 nF [T494A104M050AT]	100 nH [SRP4012TA-R10Y]
100 nF [MDS15104K250B5 3P3TUBE]	100 nF [PG224Z104MAB2S 1]	100 nF [TAJA104K035RNJ]	100 nH [SRP4020TA-R10Y]
100 nF [MDS15104K630B5 3P3TUBE]	100 nF [PG226D104MAB2S 1]	100 nF [TAJA104K050RNJ]	100 nH [SRP7030- R10FM]
100 nF [MMC7.3104K100K 31TR12]	100 nF [PG226W104MAB2 S1]	100 nF [TAJR104K035RNJ]	100 nH [SRP8040- R10Y]
100 nF [PG124D104MAB2S 1]	100 nF [PG226Z104MAB2S 1]	100 nF [TAJS104K020RNJ]	100 Ohm [4108R-1- 101]
100 nF [PG124W104MAB2 S1]	100 nF [SPC10.2104K100A 31TR16]	100 nF [TAJS104K035RNJ]	100 Ohm [4108R-1- 101LF]
100 nF [PG124Z104MAB2S 1]	100 nF [SPC12.7104K250B 31TR24]	100 nF [THJA104K035RJN]	100 Ohm [4114R-1- 101]
100 nF [PG126D104MAB2S 1]	100 nF [SPC16.5104K400C 31TR24]	100 nF [TRJA104K035RRJ]	100 Ohm [4114R-2- 101LF]
100 nF [PG126W104MAB2 S1]	100 nF [SPC16.5104K630C 31TR24]	100 nF [W2L1YC104MAT1A]	100 Ohm [4116R-1- 101]
100 nF [PG126Z104MAB2S 1]	100 nF [T491A104M035AT]	100 nF [W3L1YC104MAT1A]	100 Ohm [4116R-1- 101LF]
100 nF [PG224D104MAB2S 1]	100 nF [T491A104M050AT]	100 nF [W3L1YC104MAT1S]	100 Ohm [4116R-2- 101LF]
	100 nF [T494A104M035AT]	100 nH [SRP1235- R10M]	100 Ohm [4304M- 102-101]

Multisim 14.1 Education Components

100 Ohm [4304M-102-101LF]	100 Ohm [4308M-102-101LF]	100 Ohm [4311R-101-101]	100 Ohm [4604X-102-101LF]
100 Ohm [4306M-101-101]	100 Ohm [4308R-101-101]	100 Ohm [4416P-1-101]	100 Ohm [4604X-AP2-101LF]
100 Ohm [4306M-101-101LF]	100 Ohm [4308R-101-101LF]	100 Ohm [4416P-1-101LF]	100 Ohm [4605X-101-101LF]
100 Ohm [4306M-102-101]	100 Ohm [4308R-102-101]	100 Ohm [4416P-2-101]	100 Ohm [4606H-101-101LF]
100 Ohm [4306M-102-101LF]	100 Ohm [4308R-102-101LF]	100 Ohm [4416P-2-101LF]	100 Ohm [4606M-102-101LF]
100 Ohm [4306R-101-101]	100 Ohm [4309R-101-101]	100 Ohm [4416P-T01-101]	100 Ohm [4606X-101-101LF]
100 Ohm [4306R-101-101LF]	100 Ohm [4309R-101-101LF]	100 Ohm [4416P-T02-101]	100 Ohm [4606X-102-101LF]
100 Ohm [4306R-102-101]	100 Ohm [4310H-101-101]	100 Ohm [4420P-1-101]	100 Ohm [4606X-AP2-101LF]
100 Ohm [4306R-102-101LF]	100 Ohm [4310H-101-101LF]	100 Ohm [4420P-1-101LF]	100 Ohm [4607X-101-101LF]
100 Ohm [4308H-101-101]	100 Ohm [4310M-101-101]	100 Ohm [4420P-2-101]	100 Ohm [4608H-102-101LF]
100 Ohm [4308H-102-101]	100 Ohm [4310M-101-101LF]	100 Ohm [4420P-2-101LF]	100 Ohm [4608M-101-101LF]
100 Ohm [4308H-102-101LF]	100 Ohm [4310R-101-101]	100 Ohm [4420P-T01-101]	100 Ohm [4608M-102-101LF]
100 Ohm [4308M-101-101]	100 Ohm [4310R-101-101LF]	100 Ohm [4420P-T02-101]	100 Ohm [4608X-101-101LF]
100 Ohm [4308M-101-101LF]	100 Ohm [4310R-102-101]	100 Ohm [4420P-T04-101]	100 Ohm [4608X-102-101LF]
100 Ohm [4308M-102-101]	100 Ohm [4310R-102-101LF]	100 Ohm [4604X-101-101LF]	100 Ohm [4608X-AP1-101LF]

Multisim 14.1 Education Components

100 Ohm [4608X-AP2-101LF]	100 Ohm [4614X-102-101LF]	100 Ohm [4816P-T01-101]	100 Ohm [CAT16-101J4GLF]
100 Ohm [4609H-101-101LF]	100 Ohm [4814P-1-101]	100 Ohm [4816P-T01-101LF]	100 Ohm [CAT16-101J4LF]
100 Ohm [4609M-101-101LF]	100 Ohm [4814P-1-101LF]	100 Ohm [4816P-T02-101]	100 Ohm [CAT16-101J8LF]
100 Ohm [4609X-101-101LF]	100 Ohm [4814P-2-101]	100 Ohm [4816P-T02-101LF]	100 Ohm [CAT25-101JALF]
100 Ohm [4610H-101-101LF]	100 Ohm [4814P-2-101LF]	100 Ohm [4818P-T02-101LF]	100 Ohm [CAY10-101J2LF]
100 Ohm [4610H-102-101LF]	100 Ohm [4814P-T01-101]	100 Ohm [4820P-1-101]	100 Ohm [CAY10-101J4LF]
100 Ohm [4610M-101-101LF]	100 Ohm [4814P-T01-101LF]	100 Ohm [4820P-1-101LF]	100 Ohm [CAY16-1000F4LF]
100 Ohm [4610M-102-101LF]	100 Ohm [4814P-T02-101]	100 Ohm [4820P-2-101]	100 Ohm [CAY16-101J2LF]
100 Ohm [4610X-101-101LF]	100 Ohm [4814P-T02-101LF]	100 Ohm [4820P-2-101LF]	100 Ohm [CAY16-101J4GLF]
100 Ohm [4610X-102-101LF]	100 Ohm [4816P-1-101]	100 Ohm [4820P-T01-101]	100 Ohm [CAY16-101J4LF]
100 Ohm [4610X-AP1-101LF]	100 Ohm [4816P-1-101F]	100 Ohm [4820P-T01-101LF]	100 Ohm [CAY16-101J8LF]
100 Ohm [4610X-AP2-101LF]	100 Ohm [4816P-1-101LF]	100 Ohm [4820P-T02-101]	100 Ohm [CAY17-101JALF]
100 Ohm [4611X-101-101LF]	100 Ohm [4816P-2-101]	100 Ohm [CAT10-101J4LF]	100 Ohm [CR0201-FW-1000GLF]
100 Ohm [4612X-102-101LF]	100 Ohm [4816P-2-101LF]	100 Ohm [CAT16-1000F4LF]	100 Ohm [CR0201-JW-101GLF]
100 Ohm [4613X-101-101LF]	100 Ohm [4816P-4-101]	100 Ohm [CAT16-101J2LF]	100 Ohm [CR0402-FX-1000GLF]

Multisim 14.1 Education Components

100 Ohm [CR0402-JW-101GLF]	100 Ohm [CR2512-JW-101ELF]	100 Ohm [CRT0402-BY-1000GLF]	100 Ohm [CRT1206-DW-1000ELF]
100 Ohm [CR0603-FX-1000ELF]	100 Ohm [CRM1206-FX-1000ELF]	100 Ohm [CRT0402-BZ-1000GLF]	100 Ohm [CRT1206-FZ-1000ELF]
100 Ohm [CR0603-FX-1000HLF]	100 Ohm [CRM2010-FX-1000ELF]	100 Ohm [CRT0402-DY-1000GLF]	100 Ohm [CRT1206-PW-1000ELF]
100 Ohm [CR0603-JW-101ELF]	100 Ohm [CRM2512-FX-1000ELF]	100 Ohm [CRT0402-FZ-1000GLF]	100 Ohm [FW10A1000JA]
100 Ohm [CR0805-FX-1000ELF]	100 Ohm [CRM2512-JW-101ELF]	100 Ohm [CRT0603-BZ-1000ELF]	100 Ohm [FW20A1000JA]
100 Ohm [CR0805-JW-101ELF]	100 Ohm [CRS0805-FX-1000ELF]	100 Ohm [CRT0603-DY-1000ELF]	100 Ohm [FW30A1000JA]
100 Ohm [CR0805-JW-101GLF]	100 Ohm [CRS1206-FX-1000ELF]	100 Ohm [CRT0603-FY-1000ELF]	100 Ohm [FW50A1000JA]
100 Ohm [CR1206-FX-1000ELF]	100 Ohm [CRS1206-JX-101ELF]	100 Ohm [CRT0805-BY-1000ELF]	100 Ohm [FW70A1000JA]
100 Ohm [CR1206-FX-1000GLF]	100 Ohm [CRS2010-FX-1000ELF]	100 Ohm [CRT0805-BZ-1000ELF]	100 Ohm [PWR163S-25-1000F]
100 Ohm [CR1206-JW-101ELF]	100 Ohm [CRS2512-FX-1000ELF]	100 Ohm [CRT0805-CY-1000ELF]	100 Ohm [PWR163S-25-1000FE]
100 Ohm [CR2010-FX-1000ELF]	100 Ohm [CRT0402-BW-1000GLF]	100 Ohm [CRT0805-FX-1000ELF]	100 Ohm [PWR2010W1000JE]
100 Ohm [CR2010-JW-101ELF]			
100 Ohm [CR2512-FX-1000ELF]			

Multisim 14.1 Education Components

100 Ohm [PWR220T-20-1000J]	100 Ohm [PWR263S-35-1000FE]	100 pF [C0201C101K3GACT U]	100 pF [C0603C101K5GACT U]
100 Ohm [PWR220T-35-1000J]	100 Ohm [PWR263S-35-1000J]	100 pF [C0402C101K1HACT U]	100 pF [C0603C101K5RACT U]
100 Ohm [PWR221T-30-1000F]	100 Ohm [PWR3014W1000JE]	100 pF [C0402C101K3GACT U]	100 pF [C0603C101K8GACT U]
100 Ohm [PWR221T-30-1000J]	100 Ohm [PWR4318W1000JE]	100 pF [C0402C101K3HACT U]	100 pF [C0805C101K1GACT U]
100 Ohm [PWR221T-50-1000J]	100 Ohm [PWR4525W1000J]	100 pF [C0402C101K4GACT U]	100 pF [C0805C101K2GACT U]
100 Ohm [PWR2615W1000F]	100 Ohm [PWR4525W1000JE]	100 pF [C0402C101K5GACT U]	100 pF [C0805C101K3GACT U]
100 Ohm [PWR2615W1000J]	100 Ohm [PWR5322W1000JE]	100 pF [C0402C101K5HACT U]	100 pF [C0805C101K4GACT U]
100 Ohm [PWR2615W1000JE]	100 Ohm [PWR6327W1000J]	100 pF [C0402C101K8GACT U]	100 pF [C0805C101K5GACT U]
100 Ohm [PWR263S-20-1000F]	100 Ohm [PWR6327W1000JE]	100 pF [C0603C101K1GACT U]	100 pF [C0805C101KBGAC TU]
100 Ohm [PWR263S-20-1000FE]	100 Ohm [W1M1000J]	100 pF [C0603C101K3GACT U]	100 pF [C0805C101KCGAC TU]
100 Ohm [PWR263S-20-1000J]	100 pF [03028BR101AKZC]	100 pF [C0603C101K4GACT U]	100 pF [C0805C101KDGAC TU]
100 Ohm [PWR263S-35-1000F]			

Multisim 14.1 Education Components

100 pF [C0805H101K5GAC TU]	100 pF [C1210C101KCGAC TU]	100 pF [CA064C101K8GAC TU]	100 uF [6TPE100MI]
100 pF [C1206C101K1GACT U]	100 pF [C1210C101KDGAC TU]	100 pF [W2F11A1018AT1A]	100 uF [6TPE100MPB]
100 pF [C1206C101K2GACT U]	100 pF [C1812C101KBGAC TU]	100 pF [W3F11A1018AT1A]	100 uF [6TPG100M]
100 pF [C1206C101K3GACT U]	100 pF [C1812C101KDGAC TU]	100 uF [10TPC100M]	100 uF [6TPH100MABC]
100 pF [C1206C101K5GACT U]	100 pF [C1812C101KHGAC TU]	100 uF [16SEPC100M]	100 uF [6TPH100MAEA]
100 pF [C1206C101KBGAC TU]	100 pF [C1825C101KBGAC TU]	100 uF [16TQC100MYF]	100 uF [A700D107M006AT E015]
100 pF [C1206C101KCGAC TU]	100 pF [C2220C101KBGAC TU]	100 uF [20SVP100M]	100 uF [A700D107M006AT E018]
100 pF [C1206C101KDGAC TU]	100 pF [C2225C101KBGAC TU]	100 uF [20TQC100MYF]	100 uF [A700V107M002AT E018]
100 pF [C1206C101KGGAC TU]	100 pF [CA064C101K1GAC TU]	100 uF [6SVPC100M]	100 uF [A700V107M002AT E025]
100 pF [C1210C101K5GACT U]	100 pF [CA064C101K3GAC TU]	100 uF [6SVPC100MY]	100 uF [A700V107M002AT E028]
100 pF [C1210C101KBGAC TU]	100 pF [CA064C101K5GAC TU]	100 uF [6TPE100M]	100 uF [A700X107M008AT E010]
		100 uF [6TPE100MAZB]	

Multisim 14.1 Education Components

100 uF [A700X107M008AT E015]	100 uF [T489C107M010AT E500]	100 uF [T491D107M016AT]	100 uF [T494B107M004AT]
100 uF [A700X107M010AT E010]	100 uF [T489D107M010AT E150]	100 uF [T491D107M020AT]	100 uF [T494B107M006AT]
100 uF [A700X107M010AT E015]	100 uF [T489D107M010AT E440]	100 uF [T491E107M020AT]	100 uF [T494C107M004AT]
100 uF [EEFCT0J101R]	100 uF [T491A107M004AT]	100 uF [T491T107M004AT]	100 uF [T494C107M010AT]
100 uF [EEFCX0J101R]	100 uF [T491B107M004AT]	100 uF [T491T107M2R5AT]	100 uF [T494D107M004AT]
100 uF [EEFCX1A101R]	100 uF [T491B107M006AT]	100 uF [T491U107M004AT]	100 uF [T494D107M006AT]
100 uF [EEFHX1A101R]	100 uF [T491B107M010AT]	100 uF [T491U107M006AT]	100 uF [T494D107M010AT]
100 uF [EEFSX0G101ER]	100 uF [T491C107M004AT]	100 uF [T491V107M006AT]	100 uF [T494D107M016AT]
100 uF [EEHZA1E101XP]	100 uF [T491C107M006AT]	100 uF [T491V107M010AT]	100 uF [T494E107M020AT]
100 uF [EEHZA1H101P]	100 uF [T491C107M010AT]	100 uF [T491V107M016AT]	100 uF [T494T107M004AT]
100 uF [EEHZC1E101XP]	100 uF [T491D107M004AT]	100 uF [T491X107M016AT]	100 uF [T494T107M2R5AT]
100 uF [EEHZC1H101P]	100 uF [T491D107M006AT]	100 uF [T491X107M020AT]	100 uF [T494U107M004AT]
100 uF [ETPH100MHA]	100 uF [T491D107M010AT]	100 uF [T491X107M025AT]	
100 uF [ETPU100MSI]		100 uF [T494A107M004AT]	

Multisim 14.1 Education Components

100 uF [T494U107M006AT]	100 uF [T495D107M010AT E050]	100 uF [T495V107M010AT E150]	100 uF [T513D107M016AH 6110]
100 uF [T494V107M006AT]	100 uF [T495D107M010AT E065]	100 uF [T495X107M010AT E100]	100 uF [T513E107M025AH 6110]
100 uF [T494V107M010AT]	100 uF [T495D107M010AT E080]	100 uF [T495X107M016AT E080]	100 uF [T513X107M020AH 6110]
100 uF [T494V107M016AT]			
100 uF [T494X107M016AT]	100 uF [T495D107M010AT E100]	100 uF [T495X107M016AT E100]	100 uF [T513X107M020AH 6120]
100 uF [T494X107M020AT]	100 uF [T495D107M016AT E100]	100 uF [T495X107M020AT E100]	100 uF [T520B107M003AT E035]
100 uF [T494X107M025AT]	100 uF [T495D107M016AT E125]	100 uF [T495X107M020AT E150]	100 uF [T520B107M003AT E040]
100 uF [T495B107M006AT E400]	100 uF [T495E107M020AT E060]	100 uF [T498D107M006AT E600]	100 uF [T520B107M003AT E070]
100 uF [T495B107M006AT E700]	100 uF [T495E107M020AT E200]	100 uF [T498D107M010AT E600]	100 uF [T520B107M004AT E035]
100 uF [T495B107M010AT E350]	100 uF [T495T107M2R5AT E3K0]	100 uF [T510E107M025AT E050]	100 uF [T520B107M004AT E040]
100 uF [T495C107M006AT E150]	100 uF [T495V107M006AT E150]	100 uF [T510X107M020AT E040]	100 uF [T520B107M004AT E070]
100 uF [T495D107M006AT E050]	100 uF [T495V107M010AT E100]	100 uF [T510X107M020AT E045]	100 uF [T520B107M006AT E015]
100 uF [T495D107M006AT E130]			

Multisim 14.1 Education Components

100 uF [T520B107M006AT E018]	100 uF [T520D107M006AT E007]	100 uF [T520V107M006AT E009]	100 uF [T521X107M025AT E060]
100 uF [T520B107M006AT E025]	100 uF [T520D107M010AT E018]	100 uF [T520V107M006AT E012]	100 uF [T525B107M003AT E080]
100 uF [T520B107M006AT E035]	100 uF [T520D107M010AT E055]	100 uF [T520V107M006AT E045]	100 uF [T525B107M004AT E080]
100 uF [T520B107M006AT E040]	100 uF [T520D107M010AT E080]	100 uF [T520V107M010AT E018]	100 uF [T525D107M010AT E025]
100 uF [T520B107M006AT E070]	100 uF [T520T107M004AT E070]	100 uF [T520V107M010AT E025]	100 uF [T525D107M010AT E055]
100 uF [T520B107M2R5AT E035]	100 uF [T520T107M004AT E150]	100 uF [T520V107M010AT E045]	100 uF [T525T107M2R5AT E080]
100 uF [T520B107M2R5AT E040]	100 uF [T520T107M006AT E070]	100 uF [T520V107M010AT E050]	100 uF [T528I107M003ATE 200]
100 uF [T520C107M006AT E025]	100 uF [T520T107M2R5AT E070]	100 uF [T520W107M006AT E040]	100 uF [T540B107M004AH 6510]
100 uF [T520C107M006AT E045]	100 uF [T520U107M004AT E055]	100 uF [T520W107M010AT E040]	100 uF [T540D107M010AH 6510]
100 uF [T520C107M010AT E025]	100 uF [T520U107M006AT E055]	100 uF [T521D107M016AT E050]	100 uF [TAJA107K004RNJ]
100 uF [T520C107M010AT E045]	100 uF [T520V107M006AT E007]	100 uF [T521V107M016AT E050]	100 uF [TAJB107K004RNJ]
			100 uF [TAJB107K006RNJ]

Multisim 14.1 Education Components

100 uF [TAJC107K006RNJ]	100 uF [TAJX107K010RNJ]	100 uF [TPSC107K006R015 0]	100 uF [TPSD107K010R012 5]
100 uF [TAJC107K010RNJ]	100 uF [TAJY107K006RNJ]	100 uF [TPSC107K010R007 5]	100 uF [TPSD107K010R015 0]
100 uF [TAJC107K016RNJ]	100 uF [TAJY107K010RNJ]	100 uF [TPSC107K010R010 0]	100 uF [TPSD107K016R006 0]
100 uF [TAJD107K010RNJ]	100 uF [THJD107K010RJN]	100 uF [TPSC107K010R015 0]	100 uF [TPSD107K016R010 0]
100 uF [TAJD107K016RNJ]	100 uF [THJE107K016RJN]	100 uF [TPSC107K010R020 0]	100 uF [TPSD107K016R012 5]
100 uF [TAJE107K010RNJ]	100 uF [TPME107K020R00 35]	100 uF [TPSC107K016R020 0]	100 uF [TPSD107K016R015 0]
100 uF [TAJE107K016RNJ]	100 uF [TPME107K020R00 45]	100 uF [TPSD107K006R030 0]	100 uF [TPSD107K020R008 5]
100 uF [TAJE107K020RNJ]	100 uF [TPSB107K004R035 0]	100 uF [TPSD107K010R005 0]	100 uF [TPSD107K020R010 0]
100 uF [TAJT107K002RNJ]	100 uF [TPSB107K004R050 0]	100 uF [TPSD107K010R006 5]	100 uF [TPSD107K020R015 0]
100 uF [TAJV107K020RNJ]	100 uF [TPSB107K006R025 0]	100 uF [TPSD107K010R008 0]	100 uF [TPSE107K010R012 5]
100 uF [TAJW107K004RNJ]	100 uF [TPSB107K006R040 0]	100 uF [TPSD107K010R010 0]	100 uF [TPSE107K016R005 5]
100 uF [TAJW107K006RNJ]	100 uF [TPSC107K006R007 5]		

Multisim 14.1 Education Components

100 uF [TPSE107K016R010 0]	100 uF [TPSY107K006R010 0]	100 uH [SDE1006A- 101K]	100 uH [SDR1307- 101KL]
100 uF [TPSE107K016R012 5]	100 uF [TPSY107K010R010 0]	100 uH [SDR0302- 101KL]	100 uH [SDR1307A-101K]
100 uF [TPSE107K016R015 0]	100 uF [TPSY107K010R015 0]	100 uH [SDR0503- 101KL]	100 uH [SDR1806- 101KL]
100 uF [TPSE107K020R015 0]	100 uF [TPSY107K010R020 0]	100 uH [SDR0603- 101KL]	100 uH [SDR7030- 101K]
100 uF [TPSE107K020R020 0]	100 uF [TPSY107K016R010 0]	100 uH [SDR0604- 101KL]	100 uH [SDR7045- 101K]
100 uF [TPSV107K020R006 0]	100 uF [TPSY107K016R015 0]	100 uH [SDR0703- 101KL]	100 uH [SRN1060- 101M]
100 uF [TPSV107K020R008 5]	100 uF [TPSY107K016R020 0]	100 uH [SDR0805- 101KL]	100 uH [SRN3015- 101M]
100 uF [TPSV107K020R010 0]	100 uF [TRJD107K010RRJ]	100 uH [SDR0906- 101KL]	100 uH [SRN4018- 101M]
100 uF [TPSV107K020R020 0]	100 uF [TRJD107K016RRJ]	100 uH [SDR1005- 101KL]	100 uH [SRN4026- 101M]
100 uF [TPSX107K010R015 0]	100 uF [TRJE107K016RRJ]	100 uH [SDR1006- 101KL]	100 uH [SRN6028- 101M]
100 uF [TPSX107K010R020 0]	100 uF [TRJE107K020RRJ]	100 uH [SDR1030- 101K]	100 uH [SRN6045- 101M]
	100 uH [SDE0604A- 101K]	100 uH [SDR1045- 101K]	100 uH [SRN8040- 101M]
	100 uH [SDE0805A- 101K]	100 uH [SDR1105- 101KL]	100 uH [SRP1770TA-101M]
		100 uH [SDR1305- 101K]	100 uH [SRR0603- 101KL]

Multisim 14.1 Education Components

100 uH [SRR0604-101KL]	100 uH [SRR1210A-101M]	100 uH [SRR6603-101ML]	100 uH [SRU5028-101Y]
100 uH [SRR0618-101ML]	100 uH [SRR1240-101M]	100 uH [SRR7032-101M]	100 uH [SRU5028A-101Y]
100 uH [SRR0735A-101M]	100 uH [SRR1260-101M]	100 uH [SRR7045-101M]	100 uH [SRU6018-101Y]
100 uH [SRR0745A-101M]	100 uH [SRR1260A-101M]	100 uH [SRU1028-101Y]	100 uH [SRU6025-101Y]
100 uH [SRR0804-101K]	100 uH [SRR1280-101M]	100 uH [SRU1028A-101Y]	100 uH [SRU6025A-101Y]
100 uH [SRR0805-101K]	100 uH [SRR1806-101M]	100 uH [SRU1038-101Y]	100 uH [SRU8028-101Y]
100 uH [SRR0905-101K]	100 uH [SRR3011-101YL]	100 uH [SRU1038A-101Y]	100 uH [SRU8028A-101Y]
100 uH [SRR0906-101YL]	100 uH [SRR4011-101YL]	100 uH [SRU1048-101Y]	100 uH [SRU8043-101Y]
100 uH [SRR0908-101YL]	100 uH [SRR4018-101Y]	100 uH [SRU1048A-101Y]	10029449-001RLF
100 uH [SRR1003-101M]	100 uH [SRR4028-101Y]	100 uH [SRU1063-101Y]	100V_100W
100 uH [SRR1005-101K]	100 uH [SRR5018-101Y]	100 uH [SRU2016-101Y]	10104111-0001LF
100 uH [SRR1205-101KL]	100 uH [SRR5028-101Y]	100 uH [SRU3028-101Y]	102 kOhm [CR0201-FW-1023GLF]
100 uH [SRR1206-101YL]	100 uH [SRR6028-101Y]	100 uH [SRU5011-101Y]	102 kOhm [CR0402-FX-1023GLF]
100 uH [SRR1208-101YL]	100 uH [SRR6038-101Y]	100 uH [SRU5016-101Y]	102 kOhm [CR0603-FX-1023ELF]
100 uH [SRR1210-101M]	100 uH [SRR6040A-101M]	100 uH [SRU5018-101Y]	102 kOhm [CR0805-FX-1023ELF]

Multisim 14.1 Education Components

102 kOhm [CR1206-FX-1023ELF]	105 Ohm [CR0402-FX-1050GLF]	10BQ015	11 kOhm [CR0805-FX-1102ELF]
102 kOhm [CRT0603-BX-1023ELF]	105 Ohm [CR0603-FX-1050ELF]	10BQ040	11 kOhm [CR0805-JW-113ELF]
102 kOhm [CRT0805-BW-1023ELF]	105 Ohm [CR0603-FX-1050GLF]	10Line_Bussed	11 kOhm [CR1206-FX-1102ELF]
102 Ohm [CR0402-FX-1020GLF]	105 Ohm [CR0805-FX-1050ELF]	10Line_Isolated	11 kOhm [CR1206-JW-113ELF]
102 Ohm [CR0603-FX-1020ELF]	105 Ohm [CR1206-FX-1050ELF]	10TQ045	11 kOhm [CR2010-JW-113ELF]
102 Ohm [CR0805-FX-1020ELF]	105 Ohm [CRM2512-FX-1050ELF]	10YQ045	11 kOhm [CRM2512-FX-1102ELF]
102 Ohm [CR1206-FX-1020ELF]	105081-0001	10YQ045C	11 kOhm [CAT16-1102F4LF]
1028	107 kOhm [CR0603-FX-1073ELF]	11 kOhm [4116R-1-113]	11 kOhm [CRT0402-BY-1102GLF]
105 kOhm [CR0402-FX-1053GLF]	107 kOhm [CR0805-FX-1073ELF]	11 kOhm [4116R-1-113LF]	11 kOhm [CRT0603-BY-1102ELF]
105 kOhm [CR0603-FX-1053ELF]	107 kOhm [CR1206-FX-1073ELF]	11 kOhm [CAT16-113J4LF]	11 kOhm [CRT0603-BZ-1102ELF]
105 kOhm [CR0805-FX-1053ELF]	107 kOhm [CRT0402-BY-1073GLF]	11 kOhm [CAY16-1102F4LF]	11 kOhm [CRT0805-BW-1102ELF]
105 kOhm [CR1206-FX-1053ELF]	107 Ohm [CR0603-FX-1070ELF]	11 kOhm [CAY16-113J4LF]	11 kOhm [CRT0805-DZ-1102ELF]
105 kOhm [CRT0603-BY-1053ELF]	107 Ohm [CR0805-FX-1070ELF]	11 kOhm [CR0201-FW-1102GLF]	11 kOhm [CRT1206-BY-1102ELF]
	107 Ohm [CR1206-FX-1070ELF]	11 kOhm [CR0402-FX-1102GLF]	11 MOhm [4604X-102-116LF]

Multisim 14.1 Education Components

11 Ohm [CAY16-110J4LF]	11 Ohm [PWR6327N11R0FE]	11.3 kOhm [CR1206-FX-1132ELF]	11.5 Ohm [CR0402-FX-11R5GLF]
11 Ohm [CR0402-FX-11R0GLF]	11 pF [C0805C110KBGAC TU]	11.3 kOhm [CRT0805-BY-1132ELF]	11.5 Ohm [CR0603-FX-11R5ELF]
11 Ohm [CR0603-FX-11R0ELF]	11 pF [C1206C110KBGAC TU]	11.3 kOhm [CRT0805-DZ-1132ELF]	11.5 Ohm [CR0805-FX-11R5ELF]
11 Ohm [CR0603-JW-110ELF]	11 pF [C1210C110KBGAC TU]	11.3 Ohm [CR0201-FW-11R3GLF]	11.5 Ohm [CRT0402-FZ-11R5GLF]
11 Ohm [CR0805-FX-11R0ELF]	11 pF [C1812C110KBGAC TU]	11.3 Ohm [CR0805-FX-11R3ELF]	11.5 Ohm [CRT0805-BY-11R5ELF]
11 Ohm [CR0805-JW-110ELF]	11 pF [C1825C110KBGAC TU]	11.5 kOhm [CR0402-FX-1152GLF]	11.5 Ohm [CRT1206-BW-11R5ELF]
11 Ohm [CR1206-FX-11R0ELF]	11 pF [C2220C110KBGAC TU]	11.5 kOhm [CR0603-FX-1152ELF]	11.8 kOhm [CR0402-FX-1182GLF]
11 Ohm [CR1206-JW-110ELF]	11 pF [C2225C110KBGAC TU]	11.5 kOhm [CR0805-FX-1152ELF]	11.8 kOhm [CR0603-FX-1182ELF]
11 Ohm [CRM2512-FX-11R0ELF]	11.3 kOhm [CR0402-FX-1132GLF]	11.5 kOhm [CR1206-FX-1152ELF]	11.8 kOhm [CR0805-FX-1182ELF]
11 Ohm [CRT0805-BW-11R0ELF]	11.3 kOhm [CR0603-FX-1132ELF]	11.5 kOhm [CRT0402-FZ-1152GLF]	11.8 Ohm [CR0603-FX-11R8ELF]
11 Ohm [CRT0805-BY-11R0ELF]	11.3 kOhm [CR0805-FX-1132ELF]	11.5 kOhm [CRT1206-BY-1152ELF]	11.8 Ohm [CR0805-FX-11R8ELF]
11 Ohm [CRT1206-CW-11R0ELF]			
11 Ohm [PWR4525W11R0FE]			

Multisim 14.1 Education Components

11.8 Ohm [CR1206-FX-11R8ELF]	110 kOhm [CR1206-FX-1103ELF]	110 mOhm [CRL1206-JW-R110ELF]	110 Ohm [4610X-102-111LF]
110 kOhm [4116R-1-114]	110 kOhm [CR1206-JW-114ELF]	110 mOhm [CRL2010-FW-R110ELF]	110 Ohm [4816P-1-111]
110 kOhm [4606X-AP1-114LF]	110 kOhm [CRM2512-FX-1103ELF]	110 mOhm [CRL2010-JW-R110ELF]	110 Ohm [4816P-1-111LF]
110 kOhm [4610X-101-114LF]	110 kOhm [CRT0402-BY-1103GLF]	110 mOhm [CRL2512-FW-R110ELF]	110 Ohm [4816P-2-111]
110 kOhm [CAY16-114J4LF]	110 kOhm [CRT0603-BY-1103ELF]	110 Ohm [4116R-1-111]	110 Ohm [4816P-2-111LF]
110 kOhm [CR0402-FX-1103GLF]	110 kOhm [CRT0603-FW-1103ELF]	110 Ohm [4116R-1-111LF]	110 Ohm [4816P-T02-111]
110 kOhm [CR0402-JW-114GLF]	110 mOhm [CRL0603-FW-R110ELF]	110 Ohm [4306R-101-111]	110 Ohm [4820P-2-111F]
110 kOhm [CR0603-FX-1103ELF]	110 mOhm [CRL0603-JW-R110ELF]	110 Ohm [4308R-102-111]	110 Ohm [CAT16-1100F4LF]
110 kOhm [CR0603-FX-1103GLF]	110 mOhm [CRL0805-FW-R110ELF]	110 Ohm [4308R-102-111LF]	110 Ohm [CAT16-111J4LF]
110 kOhm [CR0603-JW-114ELF]	110 mOhm [CRL0805-JW-R110ELF]	110 Ohm [4310R-101-111]	110 Ohm [CAY16-1100F4LF]
110 kOhm [CR0805-FX-1103ELF]	110 mOhm [CRL1206-FW-R110ELF]	110 Ohm [4310R-101-111LF]	110 Ohm [CAY16-111J4LF]
110 kOhm [CR0805-JW-114ELF]		110 Ohm [4608X-101-111LF]	110 Ohm [CR0402-FX-1100GLF]
		110 Ohm [4610X-101-111LF]	110 Ohm [CR0402-JW-111GLF]
			110 Ohm [CR0603-FX-1100ELF]
			110 Ohm [CR0603-JW-111ELF]

Multisim 14.1 Education Components

110 Ohm [CR0805-FX-1100ELF]	110 pF [C0402C111K5HACT U]	113 kOhm [CR0603-FX-1133ELF]	115 Ohm [CR0402-FX-1150GLF]
110 Ohm [CR0805-FX-1100GLF]	110 pF [C0603C111K5GACT U]	113 kOhm [CR0805-FX-1133ELF]	115 Ohm [CR0603-FX-1150ELF]
110 Ohm [CR0805-JW-111ELF]	110 pF [C0805C111K1GACT U]	113 kOhm [CR1206-FX-1133ELF]	115 Ohm [CR0805-FX-1150ELF]
110 Ohm [CR1206-FX-1100ELF]	110 pF [C1206C111K5GACT U]	113 Ohm [CR0603-FX-1130ELF]	115 Ohm [CRT0805-BY-1150ELF]
110 Ohm [CR1206-JW-111ELF]	110 pF [C1206C111KBGAC TU]	113 Ohm [CR0805-FX-1130ELF]	118 kOhm [CR0402-FX-1183GLF]
110 Ohm [CR2512-FX-1100ELF]	110 pF [C1210C111KBGAC TU]	115 kOhm [CR0402-FX-1153GLF]	118 kOhm [CR0603-FX-1183ELF]
110 Ohm [CRT0402-FZ-1100GLF]	110 pF [C1812C111KBGAC TU]	115 kOhm [CR0603-FX-1153ELF]	118 kOhm [CR0805-FX-1183ELF]
110 Ohm [CRT1206-BW-1100ELF]	110 pF [C1825C111KBGAC TU]	115 kOhm [CR0805-FX-1153ELF]	118 Ohm [CR0402-FX-1180GLF]
110 Ohm [PWR220T-35-1100J]	110 pF [C2220C111KBGAC TU]	115 kOhm [CR1206-FX-1153ELF]	118 Ohm [CR0603-FX-1180ELF]
110 pF [C0402C111K1HACT U]	110 pF [C2225C111KBGAC TU]	115 kOhm [CRT0805-BY-1153ELF]	118 Ohm [CR0805-FX-1180ELF]
110 pF [C0402C111K3HACT U]	113 kOhm [CR0402-FX-1133GLF]	115 kOhm [CRT0805-FW-1153ELF]	118 Ohm [CR1206-FX-1180ELF]

Multisim 14.1 Education Components

118 Ohm [CRS1206-FX- 1180ELF]	12 kOhm [4308R- 101-123]	12 kOhm [4606X- 101-123LF]	12 kOhm [4814P-2- 123]
12 kOhm [4108R-1- 123LF]	12 kOhm [4308R- 101-123LF]	12 kOhm [4606X- 102-123LF]	12 kOhm [4814P- T02-123]
12 kOhm [4114R-1- 123]	12 kOhm [4308R- 102-123]	12 kOhm [4607X- 101-123LF]	12 kOhm [4816P-1- 123]
12 kOhm [4114R-1- 123LF]	12 kOhm [4308R- 102-123LF]	12 kOhm [4608H- 102-123LF]	12 kOhm [4816P-1- 123LF]
12 kOhm [4114R-2- 123]	12 kOhm [4309R- 101-123LF]	12 kOhm [4608X- 101-123LF]	12 kOhm [4816P-2- 123]
12 kOhm [4116R-1- 123]	12 kOhm [4310H- 101-123]	12 kOhm [4608X- 102-123LF]	12 kOhm [4816P-2- 123LF]
12 kOhm [4116R-1- 123LF]	12 kOhm [4310M- 101-123]	12 kOhm [4609X- 101-123LF]	12 kOhm [4816P- T01-123]
12 kOhm [4116R-2- 123]	12 kOhm [4310M- 101-123LF]	12 kOhm [4610H- 101-123LF]	12 kOhm [4816P- T01-123LF]
12 kOhm [4116R-2- 123LF]	12 kOhm [4310R- 101-123]	12 kOhm [4610H- 102-123LF]	12 kOhm [4816P- T02-123]
12 kOhm [4306H- 101-123]	12 kOhm [4310R- 101-123LF]	12 kOhm [4610M- 101-123LF]	12 kOhm [4816P- T02-123LF]
12 kOhm [4306H- 101-123LF]	12 kOhm [4310R- 102-123]	12 kOhm [4610X- 101-123LF]	12 kOhm [4820P-2- 123F]
12 kOhm [4306R- 101-123]	12 kOhm [4310R- 102-123LF]	12 kOhm [4610X- 102-123LF]	12 kOhm [CAT16- 1202F4LF]
12 kOhm [4306R- 101-123LF]	12 kOhm [4604X- 101-123LF]	12 kOhm [4610X- AP2-123LF]	12 kOhm [CAT16- 123J4LF]
12 kOhm [4306R- 102-123]	12 kOhm [4604X- 102-123LF]	12 kOhm [4611X- 101-123LF]	12 kOhm [CAT25- 123J4LF]
12 kOhm [4306R- 102-123LF]	12 kOhm [4605X- 101-123LF]	12 kOhm [4612X- 102-123LF]	12 kOhm [CAY16- 1202F4LF]

Multisim 14.1 Education Components

12 kOhm [CAY16-123J4LF]	12 kOhm [CRT0603-BW-1202ELF]	12 nF [C0402C123K8RACTU]	12 nF [C0805C123K3RACTU]
12 kOhm [CAY16-123J8LF]	12 kOhm [CRT0603-BY-1202ELF]	12 nF [C0402C123K9PACTU]	12 nF [C0805C123K4RACTU]
12 kOhm [CAY17-123JALF]	12 kOhm [CRT0805-BW-1202ELF]	12 nF [C0402C123K9RACTU]	12 nF [C0805C123K5GACTU]
12 kOhm [CR0402-FX-1202GLF]	12 kOhm [CRT0805-BY-1202ELF]	12 nF [C0603C123K1RACTU]	12 nF [C0805C123K5HACTU]
12 kOhm [CR0603-FX-1202ELF]	12 kOhm [CRT0805-FX-1202ELF]	12 nF [C0603C123K3RACTU]	12 nF [C0805C123K5RACTU]
12 kOhm [CR0805-FX-1202ELF]	12 kOhm [PWR4525W1202JE]	12 nF [C0603C123K4RACTU]	12 nF [C0805C123K8RACTU]
12 kOhm [CR0805-JW-123ELF]	12 mH [SDR0503-123JL]	12 nF [C0603C123K5RACTU]	12 nF [C0805C123KARACTU]
12 kOhm [CR1206-FX-1202ELF]	12 mOhm [CRF2512-FZ-R012ELF]	12 nF [C0805C123K1GACTU]	12 nF [C0805F123K1RACTU]
12 kOhm [CR1206-FX-1202GLF]	12 nF [C0402C123K4RACTU]	12 nF [C0805C123K1HACTU]	12 nF [C0805F123K3RACTU]
12 kOhm [CR1206-JW-123ELF]	12 nF [C0402C123K5RACTU]	12 nF [C0805C123K1RACTU]	12 nF [C0805F123K4RACTU]
12 kOhm [CRM1206-JW-123ELF]	12 nF [C0402C123K8PACTU]	12 nF [C0805C123K3HACTU]	12 nF [C0805F123K5RACTU]
12 kOhm [CRT0402-BY-1202GLF]			

Multisim 14.1 Education Components

12 nF [C1206C123K1HACT U]	12 nF [C1210C123K5GACT U]	12 nF [GMC7.3123K250K3 1TR12]	12 Ohm [CAT16- 120J2LF]
12 nF [C1206C123K1RACT U]	12 nF [C1210C123K5HACT U]	12 nF [GMC7.3123K63K31 TR12]	12 Ohm [CAT16- 120J4LF]
12 nF [C1206C123K2RACT U]	12 nF [C1210C123K5RACT U]	12 nF [MMC5.7123K250J 31TR12]	12 Ohm [CAT25- 120JALF]
12 nF [C1206C123K3HACT U]	12 nF [C1210C123KARACT U]	12 nF [MMC7.3123K400K 35TR12]	12 Ohm [CAY16- 120J8LF]
12 nF [C1206C123K5HACT U]	12 nF [C1812C123K1RACT U]	12 Ohm [4116R-1- 120]	12 Ohm [CR0402- FX-12R0GLF]
12 nF [C1206C123K5RACT U]	12 nF [C2220C123K2GACT U]	12 Ohm [4116R-1- 120LF]	12 Ohm [CR0402- JW-120GLF]
12 nF [C1206C123KARACT U]	12 nF [GMC5.7122K250J3 1TR12]	12 Ohm [4306R- 102-120LF]	12 Ohm [CR0603- FX-12R0ELF]
12 nF [C1210C123K1GACT U]	12 nF [GMC5.7123K100J3 1TR12]	12 Ohm [4308R- 102-120]	12 Ohm [CR0603- JW-120ELF]
12 nF [C1210C123K1HACT U]	12 nF [GMC5.7123K50J31 TR12]	12 Ohm [4308R- 102-120LF]	12 Ohm [CR0805- FX-12R0ELF]
12 nF [C1210C123K3HACT U]	12 nF [GMC7.3122K250K3 1TR12]	12 Ohm [4420P- T02-120LF]	12 Ohm [CR0805- FX-12R0GLF]
12 nF [C1210C123K4RACT U]	12 nF [GMC7.3122K63K31 TR12]	12 Ohm [4606X- 102-120LF]	12 Ohm [CR0805- JW-120ELF]
		12 Ohm [4608X- 102-120LF]	12 Ohm [CR1206- FX-12R0ELF]
		12 Ohm [4610X- 102-120LF]	12 Ohm [CR1206- JW-120ELF]
		12 Ohm [4816P-1- 120]	12 Ohm [CRM1206-FX- 12R0ELF]

Multisim 14.1 Education Components

12 Ohm [CRM2512-FX- 12R0ELF]	12 Ohm [PWR263S-35- 12R0F]	12 pF [C0805C120KBGAC TU]	12 uF [MDC10126K50A58 P7TUBE]
12 Ohm [CRM2512-JW- 120ELF]	12 Ohm [PWR263S-35- 12R0J]	12 pF [C1206C120K1GACT U]	12 uF [MDC10126K50A58 P8TUBE]
12 Ohm [CRT0603- FY-12R0ELF]	12 pF [C0201C120K3GACT U]	12 pF [C1206C120K5GACT U]	12 uH [SDE0403A- 120M]
12 Ohm [CRT1206- BY-12R0ELF]	12 pF [C0402C120K4GACT U]	12 pF [C1206C120KBGAC TU]	12 uH [SDE0604A- 120M]
12 Ohm [PWR163S-25- 12R0F]	12 pF [C0402C120K5GACT U]	12 pF [C1210C120KBGAC TU]	12 uH [SDE0805A- 120M]
12 Ohm [PWR163S-25- 12R0J]	12 pF [C0603C120K1GACT U]	12 pF [C1812C120KBGAC TU]	12 uH [SDR0302- 120ML]
12 Ohm [PWR220T-20- 12R0F]	12 pF [C0603C120K2GACT U]	12 pF [C1825C120KBGAC TU]	12 uH [SDR0403- 120ML]
12 Ohm [PWR220T-20- 12R0J]	12 pF [C0603C120K3GACT U]	12 pF [C2220C120KBGAC TU]	12 uH [SDR0503- 120ML]
12 Ohm [PWR221T-30- 12R0F]	12 pF [C0603C120K5GACT U]	12 pF [C2225C120KBGAC TU]	12 uH [SDR0603- 120ML]
12 Ohm [PWR263S-20- 12R0F]	12 pF [C0805C120K1GACT U]	12 pF [CA064C120K5GAC TU]	12 uH [SDR0604- 120ML]
12 Ohm [PWR263S-20- 12R0J]	12 pF [C0805C120K5GACT U]	12 uF [C1210C126K8PACT U]	12 uH [SDR0703- 120KL]
12 Ohm [PWR263S-20- 12R0JE]			12 uH [SDR0805- 120ML]
			12 uH [SDR0906- 120ML]
			12 uH [SDR1006- 120ML]

Multisim 14.1 Education Components

12 uH [SDR1105-120ML]	12 uH [SRR1210-120M]	12 uH [SRU1048-120Y]	12.1 Ohm [CR0402-FX-12R1GLF]
12 uH [SDR1307-120ML]	12 uH [SRR1210A-120M]	12 uH [SRU8028-120Y]	12.1 Ohm [CR0603-FX-12R1ELF]
12 uH [SDR1307A-120M]	12 uH [SRR1240-120M]	12 uH [SRU8043-120Y]	12.1 Ohm [CR0805-FX-12R1ELF]
12 uH [SRR0735A-120M]	12 uH [SRR1260-120M]	12.1 kOhm [CR0402-FX-1212GLF]	12.1 Ohm [CR0805-FX-12R1GLF]
12 uH [SRR0745A-120M]	12 uH [SRR1260A-120M]	12.1 kOhm [CR0603-FX-1212ELF]	12.1 Ohm [CR1206-FX-12R1ELF]
12 uH [SRR0804-120M]	12 uH [SRR1280-120M]	12.1 kOhm [CR0805-FX-1212ELF]	12.1 Ohm [CRM1206-FX-12R1ELF]
12 uH [SRR0805-120M]	12 uH [SRR4018-120Y]	12.1 kOhm [CR1206-FX-1212ELF]	12.1 Ohm [CRT0402-FZ-12R1GLF]
12 uH [SRR0905-120M]	12 uH [SRR4028-120Y]	12.1 kOhm [CRT0603-BY-1212ELF]	12.3 Ohm [CR0402-FX-12R3GLF]
12 uH [SRR0906-120ML]	12 uH [SRR5018-120Y]	12.1 kOhm [CRT0805-BY-1212ELF]	12.4 kOhm [CR0402-FX-1242GLF]
12 uH [SRR0908-120ML]	12 uH [SRR5028-120Y]	12.1 kOhm [CRT1206-BY-1212ELF]	12.4 kOhm [CR0603-FX-1242ELF]
12 uH [SRR1003-120M]	12 uH [SRR6028-120Y]	12.1 kOhm [CRT1206-FZ-1212ELF]	12.4 kOhm [CR0805-FX-1242ELF]
12 uH [SRR1005-120M]	12 uH [SRR6038-120Y]		
12 uH [SRR1205-120ML]	12 uH [SRR6040A-120M]		
12 uH [SRR1206-120ML]	12 uH [SRR7045-120M]		
12 uH [SRR1208-120ML]	12 uH [SRU1028-120Y]		

Multisim 14.1 Education Components

12.4 kOhm [CRT0805-BY- 1242ELF]	12.7 kOhm [CRT0603-BX- 1272ELF]	120 kOhm [4116R- 2-124LF]	120 kOhm [4310R- 102-124LF]
12.4 kOhm [CRT0805-FX- 1242ELF]	12.7 kOhm [CRT0603-BY- 1272ELF]	120 kOhm [4306R- 101-124]	120 kOhm [4416P- 2-124]
12.4 Ohm [CR0402- FX-12R4GLF]	12.7 kOhm [CRT0805-BY- 1272ELF]	120 kOhm [4306R- 101-124LF]	120 kOhm [4604X- 101-124LF]
12.4 Ohm [CR0805- FX-12R4ELF]	12.7 Ohm [CR0402- FX-12R7GLF]	120 kOhm [4306R- 102-124]	120 kOhm [4605X- 101-124LF]
12.4 Ohm [CR1206- FX-12R4ELF]	12.7 Ohm [CR0603- FX-12R7ELF]	120 kOhm [4306R- 102-124LF]	120 kOhm [4606X- 101-124LF]
12.4 Ohm [CRM1206-FX- 12R4ELF]	12.7 Ohm [CR0805- FX-12R7ELF]	120 kOhm [4308M- 101-124]	120 kOhm [4606X- 102-124LF]
12.7 kOhm [CR0402-FX- 1272GLF]	12.7 Ohm [CR1206- FX-12R7ELF]	120 kOhm [4308M- 101-124LF]	120 kOhm [4606X- AP1-124LF]
12.7 kOhm [CR0603-FX- 1272ELF]	120 kOhm [4114R- 1-124]	120 kOhm [4308R- 101-124]	120 kOhm [4608H- 102-124LF]
12.7 kOhm [CR0805-FX- 1272ELF]	120 kOhm [4114R- 1-124LF]	120 kOhm [4308R- 101-124LF]	120 kOhm [4608X- 101-124LF]
12.7 kOhm [CR1206-FX- 1272ELF]	120 kOhm [4114R- 2-124]	120 kOhm [4308R- 102-124]	120 kOhm [4608X- 102-124LF]
12.7 kOhm [CR2512-FX- 1272ELF]	120 kOhm [4114R- 2-124LF]	120 kOhm [4308R- 102-124LF]	120 kOhm [4609X- 101-124LF]
12.7 kOhm [CRT0402-BZ- 1272GAS]	120 kOhm [4116R- 1-124]	120 kOhm [4310M- 101-124]	120 kOhm [4610X- 101-124LF]
	120 kOhm [4116R- 1-124LF]	120 kOhm [4310R- 101-124]	120 kOhm [4610X- 102-124LF]
	120 kOhm [4116R- 1-124LF]	120 kOhm [4310R- 101-124LF]	120 kOhm [4610X- AP1-124LF]
	120 kOhm [4116R- 2-124]	120 kOhm [4310R- 102-124]	120 kOhm [4816P- 1-124]

Multisim 14.1 Education Components

120 kOhm [4816P-1-124LF]	120 kOhm [CR0402-JW-124GLF]	120 kOhm [CRM2512-JW-124ELF]	120 mOhm [CRM2512-FX-R120ELF]
120 kOhm [4816P-2-124]	120 kOhm [CR0603-FX-1203ELF]	120 kOhm [CRT1206-FX-1203ELF]	120 mOhm [PWR4525WR120J]
120 kOhm [4816P-2-124F]	120 kOhm [CR0603-JW-124ELF]	120 mOhm [CRL0603-FW-R120ELF]	120 mOhm [PWR4525WR120JE]
120 kOhm [4816P-T01-124]	120 kOhm [CR0805-FX-1203ELF]	120 mOhm [CRL0603-JW-R120ELF]	120 nF [C0603C124K4RACTU]
120 kOhm [4816P-T01-124LF]	120 kOhm [CR0805-JW-124ELF]	120 mOhm [CRL0805-FW-R120ELF]	120 nF [C0603C124K8RACTU]
120 kOhm [4816P-T02-124LF]	120 kOhm [CR1206-FX-1203ELF]	120 mOhm [CRL0805-JW-R120ELF]	120 nF [C0805C124K1RACTU]
120 kOhm [CAT16-124J4LF]	120 kOhm [CR1206-JW-124ELF]	120 mOhm [CRL1206-FW-R120ELF]	120 nF [C0805C124K3RACTU]
120 kOhm [CAT25-124JALF]	120 kOhm [CRM1206-FX-1203ELF]	120 mOhm [CRL1206-JW-R120ELF]	120 nF [C0805C124K4RACTU]
120 kOhm [CAY10-124J2LF]	120 kOhm [CRM1206-JW-124ELF]	120 mOhm [CRL2010-FW-R120ELF]	120 nF [C0805C124K5RACTU]
120 kOhm [CAY16-124J4LF]	120 kOhm [CRM2010-JW-124ELF]	120 mOhm [CRL2010-JW-R120ELF]	120 nF [C0805C124K8RACTU]
120 kOhm [CAY16-124J8LF]	120 kOhm [CRM2512-FX-1203ELF]	120 mOhm [CRL2512-JW-R120ELF]	120 nF [C1206C124K1RACTU]
120 kOhm [CR0402-FX-1203GLF]			

Multisim 14.1 Education Components

120 nF [C1206C124K2RACT U]	120 nF [C1210F124K4RACT U]	120 nF [C1812F124K3RACT U]	120 nF [MDC10124K630A5 8P7TUBE]
120 nF [C1206C124K3RACT U]	120 nF [C1210F124K5RACT U]	120 nF [C1812F124K5RACT U]	120 nF [MDC10124K630A5 8P8TUBE]
120 nF [C1206C124K4RACT U]	120 nF [C1812C124K1GACT U]	120 nF [C2220C124K1GACT U]	120 nF [MDC15124K100B5 3P3TUBE]
120 nF [C1206C124K5RACT U]	120 nF [C1812C124K1HACT U]	120 nF [C2220C124K5GACT U]	120 nF [MDC15124K250B5 3P3TUBE]
120 nF [C1206C124M5UAC TU]	120 nF [C1812C124K2RACT U]	120 nF [C2225C124K1RACT U]	120 nF [MDC15124K400B5 3P3TUBE]
120 nF [C1210C124K1RACT U]	120 nF [C1812C124K5GACT U]	120 nF [GMC5.7124K50J33 TR12]	120 nF [MDC15124K50B53 P3TUBE]
120 nF [C1210C124K3HACT U]	120 nF [C1812C124K5HACT U]	120 nF [GMC7.3124K63K31 TR12]	120 nF [MDK15124K50B53 P3TUBE]
120 nF [C1210C124K5HACT U]	120 nF [C1812C124K5RACT U]	120 nF [MDC10124K100A5 2P3TUBE]	120 nF [MDS15124K50B53 P3TUBE]
120 nF [C1210C124K5RACT U]	120 nF [C1812C124M1UAC TU]	120 nF [MDC10124K250A5 2P3TUBE]	120 nF [MMC7.3124K50K3 1TR12]
120 nF [C1210F124K1RACT U]	120 nF [C1812F124K1RACT U]	120 nF [MDC10124K400A5 2P3TUBE]	120 Ohm [4108R-1- 121]
120 nF [C1210F124K3RACT U]	120 nF [C1812F124K2RACT U]	120 nF [MDC10124K50A52 P3TUBE]	120 Ohm [4108R-1- 121LF]
			120 Ohm [4114R-1- 121]

Multisim 14.1 Education Components

120 Ohm [4114R-1-121LF]	120 Ohm [4308H-102-121]	120 Ohm [4310M-102-121LF]	120 Ohm [4605X-101-121LF]
120 Ohm [4114R-2-121]	120 Ohm [4308H-102-121LF]	120 Ohm [4310R-101-121]	120 Ohm [4606H-102-121LF]
120 Ohm [4114R-2-121LF]	120 Ohm [4308M-102-121]	120 Ohm [4310R-101-121LF]	120 Ohm [4606X-101-121LF]
120 Ohm [4116R-1-121]	120 Ohm [4308M-102-121LF]	120 Ohm [4310R-102-121]	120 Ohm [4606X-102-121LF]
120 Ohm [4116R-1-121LF]	120 Ohm [4308R-101-121]	120 Ohm [4310R-102-121LF]	120 Ohm [4607X-101-121LF]
120 Ohm [4116R-2-121]	120 Ohm [4308R-101-121LF]	120 Ohm [4416P-1-121]	120 Ohm [4608M-101-121LF]
120 Ohm [4116R-2-121LF]	120 Ohm [4308R-102-121]	120 Ohm [4416P-2-121]	120 Ohm [4608X-101-121LF]
120 Ohm [4304M-102-121]	120 Ohm [4308R-102-121LF]	120 Ohm [4416P-T01-121]	120 Ohm [4608X-102-121LF]
120 Ohm [4304M-102-121LF]	120 Ohm [4309R-101-121]	120 Ohm [4416P-T02-121]	120 Ohm [4609X-101-121LF]
120 Ohm [4306M-102-121]	120 Ohm [4309R-101-121LF]	120 Ohm [4420P-1-121]	120 Ohm [4610X-101-121LF]
120 Ohm [4306M-102-121LF]	120 Ohm [4310H-101-121]	120 Ohm [4420P-2-121]	120 Ohm [4610X-102-121LF]
120 Ohm [4306R-101-121]	120 Ohm [4310H-101-121LF]	120 Ohm [4420P-T01-121]	120 Ohm [4610X-AP1-121LF]
120 Ohm [4306R-101-121LF]	120 Ohm [4310H-102-121]	120 Ohm [4604X-101-121LF]	120 Ohm [4612X-101-121LF]
120 Ohm [4306R-102-121]	120 Ohm [4310H-102-121LF]	120 Ohm [4604X-102-121LF]	120 Ohm [4612X-102-121LF]
120 Ohm [4306R-102-121LF]	120 Ohm [4310M-102-121]	120 Ohm [4605M-101-121LF]	120 Ohm [4614X-102-121LF]

Multisim 14.1 Education Components

120 Ohm [4814P-1-121LF]	120 Ohm [4820P-1-121]	120 Ohm [CR0603-FX-1200ELF]	120 Ohm [CRM2512-FX-1200ELF]
120 Ohm [4814P-2-121]	120 Ohm [4820P-T01-121]	120 Ohm [CR0603-FX-1200GLF]	120 Ohm [CRM2512-JW-121ELF]
120 Ohm [4814P-T01-121]	120 Ohm [CAT10-121J4LF]	120 Ohm [CR0603-JW-121ELF]	120 Ohm [CRT0603-BY-1200ELF]
120 Ohm [4814P-T01-121LF]	120 Ohm [CAT16-1200F4LF]	120 Ohm [CR0603-JW-121GLF]	120 Ohm [CRT0805-DZ-1200ELF]
120 Ohm [4816P-1-121]	120 Ohm [CAT16-121J2LF]	120 Ohm [CR0805-FX-1200ELF]	120 Ohm [PWR163S-25-1200F]
120 Ohm [4816P-1-121LF]	120 Ohm [CAT16-121J4LF]	120 Ohm [CR0805-FX-1200GLF]	120 Ohm [PWR163S-25-1200JE]
120 Ohm [4816P-2-121]	120 Ohm [CAT16-121J8LF]	120 Ohm [CR1206-FX-1200ELF]	120 Ohm [PWR220T-20-1200F]
120 Ohm [4816P-2-121LF]	120 Ohm [CAT25-121JALF]	120 Ohm [CR1206-FX-1200GLF]	120 Ohm [PWR221T-30-1200F]
120 Ohm [4816P-4-121]	120 Ohm [CAY10-121J4LF]	120 Ohm [CR1206-JW-121ELF]	120 Ohm [PWR2615W1200FE]
120 Ohm [4816P-T01-121]	120 Ohm [CAY16-1200F4LF]	120 Ohm [CR2010-JW-121ELF]	120 Ohm [PWR263S-35-1200F]
120 Ohm [4816P-T01-121LF]	120 Ohm [CAY16-121J4LF]	120 Ohm [CR2512-JW-121ELF]	120 Ohm [PWR263S-35-1200J]
120 Ohm [4816P-T02-121]	120 Ohm [CAY17-121JALF]	120 Ohm [CRM1206-FX-1200ELF]	
120 Ohm [4818P-2-121]	120 Ohm [CR0402-FX-1200GLF]	120 Ohm [CRM2010-FX-1200ELF]	
120 Ohm [4818P-T02-121LF]	120 Ohm [CR0402-JW-121GLF]		

Multisim 14.1 Education Components

120 Ohm [PWR4525W1200F]	120 pF [C1206C121K1GACT U]	120 uF [10SVPC120M]	120 uF [A700X127M010AT E010]
120 Ohm [PWR4525W1200FE]	120 pF [C1206C121K2GACT U]	120 uF [10SVPC120MV]	120 uF [A700X127M010AT E015]
120 pF [03029BR121AKZC]	120 pF [C1206C121K5GACT U]	120 uF [16SVPC120M]	120 uF [EEFCS0G121R]
120 pF [C0402C121K1HACT U]	120 pF [C1206C121KBGAC TU]	120 uF [20SEPF120M]	120 uF [EEFCX0J121R]
120 pF [C0402C121K3HACT U]	120 pF [C1206C121KDGAC TU]	120 uF [35SVPF120M]	120 uF [EEFLR0G121R]
120 pF [C0402C121K5GACT U]	120 pF [C1206C121K5GACT TU]	120 uF [6TPE120MAZB]	120 uF [EEFSR0G121R]
120 pF [C0402C121K5HACT U]	120 pF [C1210C121KBGAC TU]	120 uF [A700D127M004AT E015]	120 uF [EEFSX0J121E7]
120 pF [C0603C121K1GACT U]	120 pF [C1812C121KBGAC TU]	120 uF [A700D127M004AT E018]	120 uF [T520B127M006AT E035]
120 pF [C0603C121K5GACT U]	120 pF [C1825C121KBGAC TU]	120 uF [A700D127M006AT E012]	120 uH [SDE0604A- 121K]
120 pF [C0805C121K1GACT U]	120 pF [C2220C121KBGAC TU]	120 uF [A700D127M006AT E015]	120 uH [SDE0805A- 121K]
120 pF [C0805C121K2GACT U]	120 pF [C2225C121KBGAC TU]	120 uF [A700D127M006AT E018]	120 uH [SDE1006A- 121K]
120 pF [C0805C121K5GACT U]	120 pF [CA064C121K5GAC TU]	120 uF [A700V127M002AT E018]	120 uH [SDR0302- 121KL]
			120 uH [SDR0403- 121KL]
			120 uH [SDR0503- 121KL]

Multisim 14.1 Education Components

120 uH [SDR0603-121KL]	120 uH [SRR1003-121M]	120 uH [SRU1028-121Y]	121 Ohm [CR0402-FX-1210GLF]
120 uH [SDR0604-121KL]	120 uH [SRR1005-121K]	120 uH [SRU1028A-121Y]	121 Ohm [CR0603-FX-1210ELF]
120 uH [SDR0703-121KL]	120 uH [SRR1205-121KL]	120LQ045	121 Ohm [CR0805-FX-1210ELF]
120 uH [SDR0805-121KL]	120 uH [SRR1206-121YL]	120LQ100	121 Ohm [CR1206-FX-1210ELF]
120 uH [SDR0906-121KL]	120 uH [SRR1208-121YL]	120V_100W	121 Ohm [CR2512-FX-1210ELF]
120 uH [SDR1006-121KL]	120 uH [SRR1210-121M]	120V_250W	121 Ohm [CRM1206-FX-1210ELF]
120 uH [SDR1307-121KL]	120 uH [SRR1210A-121M]	120V_AC_NC_RELAY_VIRTUAL	121 Ohm [CRT0402-FZ-1210GLF]
120 uH [SDR1307A-121KL]	120 uH [SRR1240-121K]	120V_AC_NO_RELAY_VIRTUAL	121 Ohm [CRT0805-BY-1210ELF]
120 uH [SDR1307A-121K]	120 uH [SRR1260-121K]	120V_AC_NONC_RELAY_VIRTUAL	121 Ohm [CRT1206-BY-1210ELF]
120 uH [SRR0735A-121M]	120 uH [SRR1260A-121K]	121 kOhm [CR0402-FX-1213GLF]	121 Ohm [CHV2512-FX-1243ELF]
120 uH [SRR0745A-121M]	120 uH [SRR1280-121K]	121 kOhm [CR0603-FX-1213ELF]	124 kOhm [CR0402-FX-1243GLF]
120 uH [SRR0804-121K]	120 uH [SRR4018-121Y]	121 kOhm [CR1206-FX-1213ELF]	124 kOhm [CR0603-FX-1243ELF]
120 uH [SRR0805-121K]	120 uH [SRR4028-121Y]	121 kOhm [CRT1206-FZ-1213ELF]	
120 uH [SRR0905-121K]	120 uH [SRR5018-121Y]	121 Ohm [CAY16-1210F4LF]	
120 uH [SRR0906-121YL]	120 uH [SRR7045-121M]		

Multisim 14.1 Education Components

124 kOhm [CR0805-FX-1243ELF]	127 kOhm [CRT0603-AZ-1273ELF]	12V_AC_NO_RELAY_VIRTUAL	13 kOhm [CR0805-FX-1302GLF]
124 kOhm [CR1206-FX-1243ELF]	127 kOhm [CRT1206-BY-1273ELF]	12V_AC_NONC_RELAY_VIRTUAL	13 kOhm [CR0805-JW-133ELF]
124 Ohm [CR0402-FX-1240GLF]	127 Ohm [CR0402-FX-1270GLF]	13 kOhm [4116R-1-133]	13 kOhm [CR0805-JW-133GLF]
124 Ohm [CR0603-FX-1240ELF]	127 Ohm [CR0603-FX-1270ELF]	13 kOhm [CAT10-133J4LF]	13 kOhm [CR1206-FX-1302ELF]
124 Ohm [CR0805-FX-1240ELF]	127 Ohm [CR0805-FX-1270ELF]	13 kOhm [CAT16-1302F4LF]	13 kOhm [CR1206-JW-133ELF]
124 Ohm [CR1206-FX-1240ELF]	127 Ohm [CR1206-FX-1270ELF]	13 kOhm [CAT16-133J4LF]	13 kOhm [CRM2512-FX-1302ELF]
124 Ohm [CRT0805-BY-1240ELF]	1-282834-0	13 kOhm [CAY10-133J4LF]	13 kOhm [CRM2512-JW-133ELF]
124 Ohm [CRT1206-BY-1240ELF]	1294	13 kOhm [CAY16-1302F4LF]	13 kOhm [CRM2512-JW-133ELF]
125 mOhm [PWR4525WR125F E]	12A02CH-TL-E	13 kOhm [CAY16-133J4LF]	13 kOhm [CRT0603-BY-1302ELF]
127 kOhm [CR0603-FX-1273ELF]	12A02MH-TL-E	13 kOhm [CR0402-FX-1302GLF]	13 kOhm [CRT0603-FY-1302ELF]
127 kOhm [CR0805-FX-1273ELF]	12AU7A	13 kOhm [CR0402-JW-133GLF]	13 kOhm [CRT0805-BW-1302ELF]
127 kOhm [CR1206-FX-1273ELF]	12AX7A	13 kOhm [CR0603-FX-1302ELF]	13 kOhm [CRT0805-BY-1302ELF]
	12BH7A	13 kOhm [CR0603-JW-133GLF]	13 Ohm [CAT10-130J4LF]
	12CGQ150	13 kOhm [CR0805-FX-1302ELF]	13 Ohm [CAT16-130J4GLF]
	12CTQ045	13 kOhm [CR0603-JW-133ELF]	
	12TQ045	13 kOhm [CR0603-JW-133GLF]	
	12V_10W		
	12V_25W		
	12V_AC_NC_RELAY_VIRTUAL		

Multisim 14.1 Education Components

13 Ohm [CAT16-130J4LF]	13 pF [C0603C130K5GACT U]	13.3 kOhm [CR0805-FX-1332ELF]	13.7 kOhm [CRT0805-BY-1372ELF]
13 Ohm [CAT25-130JALF]	13 pF [C0805C130K5GACT U]	13.3 kOhm [CR1206-FX-1332ELF]	13.7 Ohm [CR0603-FX-13R7ELF]
13 Ohm [CAY10-130J2LF]	13 pF [C0805C130KBGAC TU]	13.3 kOhm [CRT0805-BY-1332ELF]	13.7 Ohm [CRT0805-BY-13R7ELF]
13 Ohm [CAY16-130J4LF]	13 pF [C1206C130KBGAC TU]	13.3 Ohm [CR0603-FX-13R3ELF]	130 kOhm [CAY16-134J4LF]
13 Ohm [CR0402-FX-13R0GLF]	13 pF [C1210C130KBGAC TU]	13.3 Ohm [CR0805-FX-13R3ELF]	130 kOhm [CR0402-FX-1303GLF]
13 Ohm [CR0603-JW-130ELF]	13 pF [C1812C130KBGAC TU]	13.3 Ohm [CR1206-FX-13R3ELF]	130 kOhm [CR0402-JW-134GLF]
13 Ohm [CR0805-FX-13R0ELF]	13 pF [C1825C130KBGAC TU]	13.3 Ohm [CRT2512-FX-13R3ELF]	130 kOhm [CR0603-FX-1303ELF]
13 Ohm [CR0805-FX-13R0GLF]	13 pF [C2220C130KBGAC TU]	13.7 kOhm [CR0402-FX-1372GLF]	130 kOhm [CR0805-FX-1303ELF]
13 Ohm [CR0805-JW-130ELF]	13 pF [C2225C130KBGAC TU]	13.7 kOhm [CR0603-FX-1372ELF]	130 kOhm [CR0805-JW-134ELF]
13 Ohm [CR1206-FX-13R0ELF]	13.3 kOhm [CR0402-FX-1332GLF]	13.7 kOhm [CR0805-FX-1372ELF]	130 kOhm [CR1206-FX-1303ELF]
13 Ohm [CR1206-JW-130ELF]	13.3 kOhm [CR0603-FX-1332ELF]	13.7 kOhm [CR1206-FX-1372ELF]	130 kOhm [CR1206-JW-134ELF]
13 Ohm [CRM2512-JW-130ELF]			
13 pF [C0603C130K2GACT U]			

Multisim 14.1 Education Components

130 kOhm [CR2010-JW-134ELF]	130 mOhm [CRL0603-FW-R130ELF]	130 Ohm [4116R-1-131]	130 Ohm [CR0201-JW-131GLF]
130 kOhm [CRM2010-FX-1303ELF]	130 mOhm [CRL0603-JW-R130ELF]	130 Ohm [4116R-1-131LF]	130 Ohm [CR0402-FX-1300GLF]
130 kOhm [CRT0402-BY-1303GLF]	130 mOhm [CRL0805-FW-R130ELF]	130 Ohm [4308M-102-131]	130 Ohm [CR0402-JW-131GLF]
130 kOhm [CRT0603-BY-1303ELF]	130 mOhm [CRL0805-JW-R130ELF]	130 Ohm [4308M-102-131LF]	130 Ohm [CR0603-FX-1300ELF]
130 kOhm [CRT1206-BY-1303ELF]	130 mOhm [CRL1206-FW-R130ELF]	130 Ohm [4310R-102-131]	130 Ohm [CR0603-FX-1300HLF]
130 kOhm [CRT1206-BY-1303ELF]	130 mOhm [CRL1206-FW-R130ELF]	130 Ohm [4310R-102-131LF]	130 Ohm [CR0603-JW-131ELF]
130 kOhm [PWR220T-20-1303F]	130 mOhm [CRL1206-JW-R130ELF]	130 Ohm [4608X-102-131LF]	130 Ohm [CR0603-JW-131GLF]
130 kOhm [PWR220T-20-1303J]	130 mOhm [CRL2010-FW-R130ELF]	130 Ohm [4609X-101-131LF]	130 Ohm [CR0805-FX-1300ELF]
130 kOhm [PWR263S-20-1303F]	130 mOhm [CRL2010-JW-R130ELF]	130 Ohm [4816P-2-131]	130 Ohm [CR0805-JW-131ELF]
130 kOhm [PWR263S-20-1303J]	130 mOhm [CRL2512-FW-R130ELF]	130 Ohm [4816P-2-131LF]	130 Ohm [CR1206-FX-1300ELF]
130 kOhm [PWR263S-35-1303F]	130 mOhm [CRL2512-JW-R130ELF]	130 Ohm [4816P-T02-131]	130 Ohm [CR1206-JW-131ELF]
130 kOhm [PWR263S-35-1303J]	130 mOhm [CRM1206-JX-R130ELF]	130 Ohm [4816P-T02-131LF]	130 Ohm [CRM2512-FX-1300ELF]
		130 Ohm [CAT16-131J4LF]	130 Ohm [CRT0402-DY-1300GLF]
		130 Ohm [CAT25-131JALF]	130 Ohm [CRT0805-BY-1300ELF]

Multisim 14.1 Education Components

130 Ohm [PWR263S-20-1300J]	130 pF [C2220C131KBGAC TU]	133 Ohm [CR2010-FX-1330ELF]	14 kOhm [CR0402-FX-1402GLF]
130 Ohm [PWR263S-35-1300J]	130 pF [C2225C131KBGAC TU]	133 Ohm [CRT0402-FZ-1330GLF]	14 kOhm [CR0603-FX-1402ELF]
130 Ohm [PWR5322W1300JE]	133 kOhm [CR0402-FX-1333GLF]	135 Ohm [PWR4525W1350F]	14 kOhm [CR0805-FX-1402ELF]
130 pF [C0402C131K1HACT U]	133 kOhm [CR0603-FX-1333ELF]	135 Ohm [PWR4525W1350FE]	14 kOhm [CRT0402-CY-1402GLF]
130 pF [C0402C131K3HACT U]	133 kOhm [CR0805-FX-1333ELF]	137 kOhm [CAT16-1373F4LF]	14 Ohm [CAY16-14R0F4LF]
130 pF [C0402C131K5HACT U]	133 kOhm [CR1206-FX-1333ELF]	137 kOhm [CR0402-FX-1373GLF]	14 Ohm [CR0402-FX-14R0GLF]
130 pF [C0805H131K3GAC TU]	133 kOhm [CRT0603-AZ-1333ELF]	137 kOhm [CR0603-FX-1373ELF]	14 Ohm [CR0805-FX-14R0ELF]
130 pF [C1206C131KBGAC TU]	133 kOhm [CRT0805-BY-1333ELF]	137 kOhm [CR1206-FX-1373ELF]	14 Ohm [CR1206-FX-14R0ELF]
130 pF [C1210C131KBGAC TU]	133 Ohm [CR0402-FX-1330GLF]	137 Ohm [CR0402-FX-1370GLF]	14.3 kOhm [CR0402-FX-1432GLF]
130 pF [C1812C131KBGAC TU]	133 Ohm [CR0603-FX-1330ELF]	137 Ohm [CR0603-FX-1370ELF]	14.3 kOhm [CR0805-FX-1432ELF]
130 pF [C1825C131KBGAC TU]	133 Ohm [CR0805-FX-1330ELF]	137 Ohm [CR0805-FX-1370ELF]	14.3 kOhm [CR1206-FX-1432ELF]
	133 Ohm [CR1206-FX-1330ELF]	137 Ohm [CR1206-FX-1370ELF]	

Multisim 14.1 Education Components

14.3 Ohm [CR0402-FX-14R3GLF]	14.7 Ohm [CR1206-FX-14R7ELF]	143 kOhm [CR0603-FX-1433ELF]	147 kOhm [CRT0402-BY-1473GLF]
14.3 Ohm [CR0603-FX-14R3ELF]	14.7 Ohm [CRT0402-FZ-14R7GLF]	143 kOhm [CR0805-FX-1433ELF]	147 Ohm [CR0603-FX-1470ELF]
14.3 Ohm [CR0805-FX-14R3ELF]	140 kOhm [CR0402-FX-1403GLF]	143 kOhm [CR1206-FX-1433ELF]	147 Ohm [CR0805-FX-1470ELF]
14.3 Ohm [CR1206-FX-14R3ELF]	140 kOhm [CR0603-FX-1403ELF]	143 kOhm [CRT0603-AZ-1433ELF]	147 Ohm [CRT0402-FZ-1470GLF]
14.7 kOhm [CR0402-FX-1472GLF]	140 kOhm [CR0805-FX-1403ELF]	143 Ohm [CR0402-FX-1430GLF]	15 kOhm [4108R-1-153LF]
14.7 kOhm [CR0603-FX-1472ELF]	140 kOhm [CR1206-FX-1403ELF]	143 Ohm [CR0603-FX-1430ELF]	15 kOhm [4114R-1-153]
14.7 kOhm [CR0805-FX-1472ELF]	140 Ohm [CAT16-1400F4LF]	143 Ohm [CR0805-FX-1430ELF]	15 kOhm [4114R-1-153LF]
14.7 kOhm [CR1206-FX-1472ELF]	140 Ohm [CAT25-141JALF]	143 Ohm [CR1206-FX-1430ELF]	15 kOhm [4114R-2-153]
14.7 kOhm [CRT0402-BX-1472GLF]	140 Ohm [CR0402-FX-1400GLF]	147 kOhm [CR0402-FX-1473GLF]	15 kOhm [4114R-2-153LF]
14.7 kOhm [CRT0805-BY-1472ELF]	140 Ohm [CR0603-FX-1400ELF]	147 kOhm [CR0603-FX-1473ELF]	15 kOhm [4116R-1-153]
14.7 Ohm [CR0402-FX-14R7GLF]	140 Ohm [CR0805-FX-1400ELF]	147 kOhm [CR0805-FX-1473ELF]	15 kOhm [4116R-1-153LF]
14.7 Ohm [CR0603-FX-14R7ELF]	140 Ohm [CR1206-FX-1400ELF]	147 kOhm [CR1206-FX-1473ELF]	15 kOhm [4116R-2-153]
14.7 Ohm [CR0805-FX-14R7ELF]	143 kOhm [CR0402-FX-1433GLF]		15 kOhm [4116R-2-153LF]
			15 kOhm [4306H-101-153]

Multisim 14.1 Education Components

15 kOhm [4306H-101-153LF]	15 kOhm [4308R-102-153LF]	15 kOhm [4420P-2-153]	15 kOhm [4608X-AP2-153LF]
15 kOhm [4306M-101-153]	15 kOhm [4309R-101-153]	15 kOhm [4420P-T02-153]	15 kOhm [4609H-101-153LF]
15 kOhm [4306M-101-153LF]	15 kOhm [4309R-101-153LF]	15 kOhm [4604X-101-153LF]	15 kOhm [4609X-101-153LF]
15 kOhm [4306M-102-153]	15 kOhm [4310H-101-153]	15 kOhm [4604X-102-153LF]	15 kOhm [4610X-101-153LF]
15 kOhm [4306M-102-153LF]	15 kOhm [4310H-101-153LF]	15 kOhm [4605H-101-153LF]	15 kOhm [4610X-102-153LF]
15 kOhm [4306R-101-153]	15 kOhm [4310M-101-153]	15 kOhm [4605X-101-153LF]	15 kOhm [4610X-AP1-153LF]
15 kOhm [4306R-101-153LF]	15 kOhm [4310M-101-153LF]	15 kOhm [4606X-101-153LF]	15 kOhm [4814P-1-153]
15 kOhm [4306R-102-153]	15 kOhm [4310M-102-153]	15 kOhm [4606X-102-153LF]	15 kOhm [4814P-1-153LF]
15 kOhm [4306R-102-153LF]	15 kOhm [4310M-102-153LF]	15 kOhm [4606X-AP2-153LF]	15 kOhm [4814P-2-153]
15 kOhm [4308H-101-153]	15 kOhm [4310R-101-153]	15 kOhm [4607M-101-153LF]	15 kOhm [4814P-2-153LF]
15 kOhm [4308H-102-153]	15 kOhm [4310R-101-153LF]	15 kOhm [4607X-101-153LF]	15 kOhm [4814P-T01-153]
15 kOhm [4308H-102-153LF]	15 kOhm [4310R-102-153]	15 kOhm [4608H-102-153LF]	15 kOhm [4814P-T01-153LF]
15 kOhm [4308R-101-153]	15 kOhm [4310R-102-153LF]	15 kOhm [4608X-101-153LF]	15 kOhm [4814P-T02-153]
15 kOhm [4308R-101-153LF]	15 kOhm [4416P-1-153]	15 kOhm [4608X-102-153LF]	15 kOhm [4814P-T02-153LF]
15 kOhm [4308R-102-153]	15 kOhm [4416P-T01-153]	15 kOhm [4608X-AP1-153LF]	15 kOhm [4816P-1-153]

Multisim 14.1 Education Components

15 kOhm [4816P-1-153LF]	15 kOhm [CAT16-153J4LF]	15 kOhm [CR0603-JW-153GLF]	15 kOhm [CRT0603-PW-1502ELF]
15 kOhm [4816P-2-153]	15 kOhm [CAT16-153J8LF]	15 kOhm [CR0805-FX-1502ELF]	15 kOhm [CRT0805-BY-1502ELF]
15 kOhm [4816P-2-153LF]	15 kOhm [CAT25-153JALF]	15 kOhm [CR0805-JW-153ELF]	15 kOhm [CRT0805-DY-1502ELF]
15 kOhm [4816P-T01-153]	15 kOhm [CAY10-153J2LF]	15 kOhm [CR0805-JW-153GLF]	15 kOhm [PWR220T-20-1502J]
15 kOhm [4816P-T01-153LF]	15 kOhm [CAY10-153J4LF]	15 kOhm [CR1206-FX-1502ELF]	15 kOhm [PWR220T-35-1502J]
15 kOhm [4816P-T02-153]	15 kOhm [CAY16-1502F4LF]	15 kOhm [CR1206-JW-153ELF]	15 kOhm [PWR221T-30-1502F]
15 kOhm [4816P-T02-153LF]	15 kOhm [CAY16-153J4LF]	15 kOhm [CR2512-JW-153ELF]	15 kOhm [PWR263S-20-1502F]
15 kOhm [4818P-2-153]	15 kOhm [CAY16-153J8LF]	15 kOhm [CRM1206-FX-1502ELF]	15 kOhm [PWR263S-20-1502J]
15 kOhm [4818P-T02-153]	15 kOhm [CAY17-153JALF]	15 kOhm [CRM1206-JW-153ELF]	15 kOhm [PWR4525W1502FE]
15 kOhm [4820P-2-153]	15 kOhm [CR0201-FW-1502GLF]	15 kOhm [CRM2512-FX-1502ELF]	15 kOhm [PWR4525W1502J]
15 kOhm [4820P-T01-153]	15 kOhm [CR0201-JW-153GLF]	15 kOhm [CRM2512-JW-153ELF]	15 kOhm [PWR4525W1502JE]
15 kOhm [4820P-T02-153]	15 kOhm [CR0402-FX-1502GLF]	15 kOhm [CRM2512-JW-153ELF]	
15 kOhm [CAT10-153J4LF]	15 kOhm [CR0402-JW-153GLF]	15 kOhm [CRT0402-BY-1502GLF]	
15 kOhm [CAT16-1502F4LF]	15 kOhm [CR0603-FX-1502ELF]	15 kOhm [CRT0603-BY-1502ELF]	
15 kOhm [CAT16-1502F8LF]	15 kOhm [CR0603-JW-153ELF]		

Multisim 14.1 Education Components

15 kOhm [PWR5322W1502JE]	15 mOhm [PWR2615WR015J] 15 mOhm [PWR2615WR015JE]	15 nF [06125C153KAT2W]	15 nF [C0805C153K1GACT U]
15 kOhm [PWR6327W1502J]		15 nF [C0402C153K4RACT U]	15 nF [C0805C153K1HACT U]
15 kOhm [PWR6327W1502JE]	15 mOhm [PWR4412- 2SBR0150F]	15 nF [C0402C153K5RACT U]	15 nF [C0805C153K1RACT U]
15 mH [SDR0503- 153JL]	15 mOhm [PWR4412- 2SCR0150F]	15 nF [C0402C153K8PACT U]	15 nF [C0805C153K3HACT U]
15 mH [SRR0908- 153YL]	15 mOhm [PWR4412- 2SDR0150F]	15 nF [C0402C153K8RACT U]	15 nF [C0805C153K3RACT U]
15 mOhm [CRA2512-FZ- R015ELF]	15 mOhm [PWR4412- 2SDR0150J]	15 nF [C0402C153K9PACT U]	15 nF [C0805C153K4RACT U]
15 mOhm [CRF2512-FZ- R015ELF]	15 mOhm [PWR4525WR015J]	15 nF [C0402C153K9RACT U]	15 nF [C0805C153K5GACT U]
15 mOhm [PWR1913WR015F]	15 mOhm [PWR4525WR015JE]	15 nF [C0603C153K1RACT U]	15 nF [C0805C153K5HACT U]
15 mOhm [PWR1913WR015F E]	15 mOhm [PWR6327WR015J]	15 nF [C0603C153K3RACT U]	15 nF [C0805C153K5RACT U]
15 mOhm [PWR1913WR015J]	15 mOhm [PWR6327WR015JE]	15 nF [C0603C153K4RACT U]	15 nF [C0805C153K8RACT U]
15 mOhm [PWR1913WR015JE]	15 nF [03063C153KAT2A]	15 nF [C0603C153K5RACT U]	15 nF [C0805C153KARACT U]
15 mOhm [PWR2615WR015F]	15 nF [0306YC153KAT2A]		
15 mOhm [PWR2615WR015F E]	15 nF [0306ZC153KAT2A]		

Multisim 14.1 Education Components

15 nF [C0805C153M5UAC TU]	15 nF [C1206C153K5RACT U]	15 nF [C1812C153K1GACT U]	15 nF [GMC5.7152K250J3 1TR12]
15 nF [C0805F153K1RACT U]	15 nF [C1206C153KARACT U]	15 nF [C1812C153K1HACT U]	15 nF [GMC5.7153K100J3 1TR12]
15 nF [C0805F153K3RACT U]	15 nF [C1206C153M5UAC TU]	15 nF [C1812C153K1RACT U]	15 nF [GMC5.7153K50J31 TR12]
15 nF [C0805F153K4RACT U]	15 nF [C1210C153K1GACT U]	15 nF [C1812C153K2RACT U]	15 nF [GMC7.3152K250K3 1TR12]
15 nF [C0805F153K5RACT U]	15 nF [C1210C153K1HACT U]	15 nF [C1812C153K5GACT U]	15 nF [GMC7.3152K63K31 TR12]
15 nF [C1206C153K1HACT U]	15 nF [C1210C153K1RACT U]	15 nF [C1812C153K5HACT U]	15 nF [GMC7.3153K250K3 1TR12]
15 nF [C1206C153K1RACT U]	15 nF [C1210C153K2RACT U]	15 nF [C1812C153K5RACT U]	15 nF [GMC7.3153K63K31 TR12]
15 nF [C1206C153K2RACT U]	15 nF [C1210C153K3HACT U]	15 nF [C1825C153K5GACT U]	15 nF [GPC7.3153K63K31 TR12]
15 nF [C1206C153K3HACT U]	15 nF [C1210C153K5HACT U]	15 nF [C2220C153K2GACT U]	15 nF [LD17YC153KAB2S]
15 nF [C1206C153K4RACT U]	15 nF [C1210C153K5RACT U]	15 nF [C2225C153K5GACT U]	15 nF [MMC5.7153K250J 33TR12]
15 nF [C1206C153K5HACT U]	15 nF [C1210C153KARACT U]	15 nF [CA064C153K5RACT U]	15 nF [MMC5.7153K50J3 1TR12]

Multisim 14.1 Education Components

15 nF [MMC7.3153K250K 31TR12]	15 Ohm [4116R-2- 150]	15 Ohm [CAT16- 150J2LF]	15 Ohm [CR0603- JW-150GLF]
15 nF [MMC7.3153K400K 37TR12]	15 Ohm [4116R-2- 150LF]	15 Ohm [CAT16- 150J4LF]	15 Ohm [CR0805- FX-15R0ELF]
15 nF [MMC7.3153K50K3 1TR12]	15 Ohm [4308H- 102-150]	15 Ohm [CAT16- 15R0F4LF]	15 Ohm [CR0805- JW-150ELF]
15 nF [SPC10.2153K100A 31TR16]	15 Ohm [4416P- T01-150]	15 Ohm [CAY10- 150J2LF]	15 Ohm [CR1206- FX-15R0ELF]
15 nF [SPC10.2153K250A 31TR16]	15 Ohm [4606X- 102-150LF]	15 Ohm [CAY10- 150J4LF]	15 Ohm [CR1206- JW-150ELF]
15 nF [SPC10.2153K400A 31TR16]	15 Ohm [4608X- 102-150LF]	15 Ohm [CAY16- 150J4LF]	15 Ohm [CR2010- FX-15R0ELF]
15 nF [SPC10.2153K630A 31TR16]	15 Ohm [4609X- 101-150LF]	15 Ohm [CAY16- 150J8LF]	15 Ohm [CR2010- JW-150ELF]
15 nF [SPC7.3153K100K33 TR12]	15 Ohm [4610X- 101-150LF]	15 Ohm [CAY16- 15R0F4LF]	15 Ohm [CR2512- FX-15R0ELF]
15 nF [SPC7.3153K250K37 TR12]	15 Ohm [4816P-1- 150]	15 Ohm [CR0201- FW-15R0GLF]	15 Ohm [CRM1206-FX- 15R0ELF]
15 Ohm [4114R-1- 150LF]	15 Ohm [4816P-1- 150LF]	15 Ohm [CR0201- JW-150GLF]	15 Ohm [CRM2010-FX- 15R0ELF]
15 Ohm [4116R-1- 150]	15 Ohm [4816P- T01-150]	15 Ohm [CR0402- FX-15R0GLF]	15 Ohm [CRM2512-FX- 15R0ELF]
15 Ohm [4116R-1- 150LF]	15 Ohm [4816P- T01-150LF]	15 Ohm [CR0402- JW-150GLF]	15 Ohm [CRM2512-JW- 150ELF]
	15 Ohm [4820P- T01-150]	15 Ohm [CR0603- FX-15R0ELF]	15 Ohm [CRT0402- DZ-15R0GLF]
	15 Ohm [CAT10- 150J4LF]	15 Ohm [CR0603- JW-150ELF]	

Multisim 14.1 Education Components

15 Ohm [CRT0603-BZ-15R0EAS]	15 Ohm [PWR2010W15R0JE]	15 Ohm [PWR263S-20-15R0FE]	15 pF [C0402C150K4GACT U]
15 Ohm [CRT0805-BY-15R0ELF]	15 Ohm [PWR220T-20-15R0F]	15 Ohm [PWR263S-20-15R0J]	15 pF [C0402C150K5GACT U]
15 Ohm [CRT0805-DY-15R0ELF]	15 Ohm [PWR220T-20-15R0J]	15 Ohm [PWR263S-35-15R0F]	15 pF [C0402C150K8GACT U]
15 Ohm [FW10A15R0JA]	15 Ohm [PWR220T-35-15R0F]	15 Ohm [PWR263S-35-15R0FE]	15 pF [C0603C150K1GACT U]
15 Ohm [FW20A15R0JA]	15 Ohm [PWR220T-35-15R0J]	15 Ohm [PWR263S-35-15R0J]	15 pF [C0603C150K2GACT U]
15 Ohm [FW30A15R0JA]	15 Ohm [PWR221T-30-15R0F]	15 Ohm [PWR4318W15R0JE]	15 pF [C0603C150K4GACT U]
15 Ohm [FW50A15R0JA]	15 Ohm [PWR221T-30-15R0J]	15 Ohm [PWR4525W15R0J]	15 pF [C0603C150K5GACT U]
15 Ohm [PWR163S-25-15R0F]	15 Ohm [PWR221T-50-15R0J]	15 Ohm [PWR4525W15R0JE]	15 pF [C0805C150K1GACT U]
15 Ohm [PWR163S-25-15R0FE]	15 Ohm [PWR2615W15R0J]	15 Ohm [PWR6327W15R0J]	15 pF [C0805C150K2GACT U]
15 Ohm [PWR163S-25-15R0J]	15 Ohm [PWR2615W15R0JE]	15 Ohm [PWR6327W15R0JE]	15 pF [C0805C150K3GACT U]
15 Ohm [PWR163S-25-15R0JE]	15 Ohm [PWR263S-20-15R0F]	15 pF [C0201C150K3GACT U]	15 pF [C0805C150K4GACT U]
		15 pF [C0402C150K3GACT U]	

Multisim 14.1 Education Components

15 pF [C0805C150K5GACT U]	15 pF [C2225C150KBGAC TU]	15 uF [EEFCS1D150R]	15 uF [T419B156M004AH 4250]
15 pF [C0805C150KBGAC TU]	15 pF [CA064C150K4GAC TU]	15 uF [EEFCS1E150R]	15 uF [T419D156M010AH 4250]
15 pF [C1206C150K1GACT U]	15 pF [CA064C150K5GAC TU]	15 uF [EEFCX1C150R]	15 uF [T429B156M004AH 4250]
15 pF [C1206C150K2GACT U]	15 uF [12TPC15M] 15 uF [16TQC15M]	15 uF [EEFCX1E150R]	15 uF [T429F156M010AH 4250]
15 pF [C1206C150K5GACT U]	15 uF [25TQC15MV] 15 uF [25TQC15MYFB]	15 uF [EEFCX1V150R]	15 uF [T429F156M020AH 4250]
15 pF [C1206C150KBGAC TU]	15 uF [25TQC15MYFD]	15 uF [EEFHX1E150R]	15 uF [T489D156M025AT E300]
15 pF [C1206C150KGGAC TU]	15 uF [A700V156M12RAT E040]	15 uF [MDC10156K50A58 P7TUBE]	15 uF [T491A156M004AT]
15 pF [C1210C150KBGAC TU]	15 uF [C1210C156K4PACT U]	15 uF [MDC10156K50A58 P8TUBE]	15 uF [T491A156M006AT]
15 pF [C1812C150KBGAC TU]	15 uF [C1210C156K8PACT U]	15 uF [MMC16.5156K50C 31TR24]	15 uF [T491B156M004AT]
15 pF [C1825C150KBGAC TU]	15 uF [C1210C156K9PACT U]	15 uF [T409E156M004AH 4250]	15 uF [T491B156M006AT]
15 pF [C2220C150KBGAC TU]	15 uF [EEFCS1C150R]	15 uF [T409H156M025AH 4250]	15 uF [T491B156M010AT]
			15 uF [T491B156M016AT]

Multisim 14.1 Education Components

15 uF [T491B156M025AT]	15 uF [T491U156M016AT]	15 uF [T494C156M025AT]	15 uF [T495B156M010AT E500]
15 uF [T491C156M006AT]	15 uF [T491X156M035AT]	15 uF [T494D156M020AT]	15 uF [T495C156M010AT E375]
15 uF [T491C156M010AT]	15 uF [T491X156M050AT]	15 uF [T494D156M025AT]	15 uF [T495C156M010AT E400]
15 uF [T491C156M016AT]	15 uF [T494A156M004AT]	15 uF [T494D156M035AT]	15 uF [T495D156M020AT E275]
15 uF [T491C156M025AT]	15 uF [T494A156M006AT]	15 uF [T494S156M004AT]	15 uF [T495D156M025AT E100]
15 uF [T491D156M020AT]	15 uF [T494A156M010AT]	15 uF [T494S156M006AT]	15 uF [T495D156M025AT E275]
15 uF [T491D156M025AT]	15 uF [T494B156M004AT]	15 uF [T494T156M004AT]	15 uF [T495D156M035AT E225]
15 uF [T491D156M035AT]	15 uF [T494B156M010AT]	15 uF [T494T156M006AT]	15 uF [T495D156M035AT E300]
15 uF [T491S156M004AT]	15 uF [T494B156M016AT]	15 uF [T494T156M010AT]	15 uF [T495X156M025AT E200]
15 uF [T491S156M006AT]	15 uF [T494B156M025AT]	15 uF [T494U156M010AT]	15 uF [T495X156M035AT E200]
15 uF [T491T156M004AT]	15 uF [T494C156M006AT]	15 uF [T494U156M016AT]	15 uF [T495X156M050AT E200]
15 uF [T491T156M006AT]	15 uF [T494C156M010AT]	15 uF [T494X156M035AT]	
15 uF [T491T156M010AT]	15 uF [T494C156M016AT]	15 uF [T494X156M050AT]	
15 uF [T491U156M010AT]	15 uF [T494C156M020AT]		

Multisim 14.1 Education Components

15 uF [T495X156M050AT E300]	15 uF [T520D156M025AT E060]	15 uF [T541X156M063AH 6510]	15 uF [TAJC156K025RNJ]
15 uF [T497E156M010AT 6110]	15 uF [T520D156M025AT E080]	15 uF [T543T156M006AT E100]	15 uF [TAJC156K035RNJ]
15 uF [T498B156M006AT E1K8]	15 uF [T520T156M004AT E100]	15 uF [TACR156K003RTA]	15 uF [TAJD156K025RNJ]
15 uF [T498B156M010AT E1K5]	15 uF [T520T156M006AT E100]	15 uF [TACR156K004RTA]	15 uF [TAJD156K035RNJ]
15 uF [T498C156M010AT E1K8]	15 uF [T520T156M12RAT E080]	15 uF [TACR156K006RTA]	15 uF [TAJD156K050RNJ]
15 uF [T498C156M016AT E1K1]	15 uF [T521B156M016AT E090]	15 uF [TAJA156K006RNJ]	15 uF [TAJP156K006RNJ]
15 uF [T498D156M025AT E700]	15 uF [T521V156M025AT E090]	15 uF [TAJA156K010RNJ]	15 uF [TAJR156K004RNJ]
15 uF [T499B156M006AT E3K5]	15 uF [T521V156M035AT E100]	15 uF [TAJB156K006RNJ]	15 uF [TAJS156K004RNJ]
15 uF [T499D156M020AT E1K0]	15 uF [T521V156M035AT E125]	15 uF [TAJB156K016RNJ]	15 uF [TAJT156K006RNJ]
15 uF [T513D156M035AH 6110]	15 uF [T521X156M063AT E035]	15 uF [TAJB156K020RNJ]	15 uF [TAJT156K010RNJ]
15 uF [T520A156M010AT E080]	15 uF [T521X156M063AT E150]	15 uF [TAJC156K010RNJ]	15 uF [TAJW156K020RNJ]
		15 uF [TAJC156K016RNJ]	15 uF [TAJY156K025RNJ]
		15 uF [TAJC156K020RNJ]	

Multisim 14.1 Education Components

15 uF [TAJY156K035RNJ]	15 uF [TPSC156K016R070 0]	15 uF [TRJB156K020RRJ]	15 uH [SDR1006- 150ML]
15 uF [THJB156K006RJN]	15 uF [TPSC156K020R040 0]	15 uF [TRJD156K035RRJ]	15 uH [SDR1030- 150M]
15 uF [THJB156K010RJN]	15 uF [TPSC156K020R045 0]	15 uH [SDE0403A- 150M]	15 uH [SDR1045- 150M]
15 uF [THJC156K020RJN]	15 uF [TPSC156K025R030 0]	15 uH [SDE0604A- 150M]	15 uH [SDR1105- 150ML]
15 uF [THJD156K035RJN]	15 uF [TPSC156K035R045 0]	15 uH [SDE0805A- 150M]	15 uH [SDR1305- 150M]
15 uF [TPME156K050R00 75]	15 uF [TPSC156K035R045 0]	15 uH [SDE1006A- 150M]	15 uH [SDR1307- 150ML]
15 uF [TPME156K050R01 00]	15 uF [TPSD156K025R010 0]	15 uH [SDR0302- 150ML]	15 uH [SDR1307A- 150M]
15 uF [TPSA156K006R070 0]	15 uF [TPSD156K025R030 0]	15 uH [SDR0403- 150ML]	15 uH [SDR1806- 150ML]
15 uF [TPSA156K006R150 0]	15 uF [TPSD156K035R010 0]	15 uH [SDR0503- 150ML]	15 uH [SDR6603- 150M]
15 uF [TPSA156K010R100 0]	15 uF [TPSD156K035R030 0]	15 uH [SDR0603- 150ML]	15 uH [SDR7030- 150M]
15 uF [TPSA156K010R060 0]	15 uF [TPSD156K035R030 0]	15 uH [SDR0604- 150YL]	15 uH [SDR7045- 150M]
15 uF [TPSB156K010R060 0]	15 uF [TPSV156K050R025 0]	15 uH [SDR0703- 150KL]	15 uH [SRN3010- 150M]
15 uF [TPSB156K016R080 0]	15 uF [TRJA156K010RRJ]	15 uH [SDR0805- 150ML]	15 uH [SRN3015- 150M]
	15 uF [TRJB156K016RRJ]	15 uH [SDR0906- 150ML]	15 uH [SRN4012T- 150M]
		15 uH [SDR1005- 150ML]	15 uH [SRN4018- 150M]

Multisim 14.1 Education Components

15 uH [SRN4026-150M]	15 uH [SRR0618-150ML]	15 uH [SRR1240-150M]	15 uH [SRR7032-150M]
15 uH [SRN5020-150M]	15 uH [SRR0735A-150M]	15 uH [SRR1260-150M]	15 uH [SRR7045-150M]
15 uH [SRN5040-150M]	15 uH [SRR0745A-150M]	15 uH [SRR1260A-150M]	15 uH [SRU1028-150Y]
15 uH [SRN6028-150M]	15 uH [SRR0804-150M]	15 uH [SRR1280-150M]	15 uH [SRU1028A-150Y]
15 uH [SRN6045-150M]	15 uH [SRR0805-150M]	15 uH [SRR1806-150M]	15 uH [SRU1038-150Y]
15 uH [SRN8040-150M]	15 uH [SRR0905-150M]	15 uH [SRR3011-150YL]	15 uH [SRU1038A-150Y]
15 uH [SRP1038A-150M]	15 uH [SRR0906-150ML]	15 uH [SRR4011-150YL]	15 uH [SRU1048-150Y]
15 uH [SRP1040-150M]	15 uH [SRR0908-150ML]	15 uH [SRR4018-150Y]	15 uH [SRU1048A-150Y]
15 uH [SRP1265A-150M]	15 uH [SRR1003-150M]	15 uH [SRR4028-150Y]	15 uH [SRU1063-150Y]
15 uH [SRP1770TA-150M]	15 uH [SRR1005-150M]	15 uH [SRR5018-150Y]	15 uH [SRU2009-150Y]
15 uH [SRP4020TA-150M]	15 uH [SRR1205-150ML]	15 uH [SRR5028-150Y]	15 uH [SRU2011-150Y]
15 uH [SRP6540-150M]	15 uH [SRR1206-150ML]	15 uH [SRR6028-150Y]	15 uH [SRU2013-150Y]
15 uH [SRP7050TA-150M]	15 uH [SRR1208-150ML]	15 uH [SRR6038-150Y]	15 uH [SRU2016-150Y]
15 uH [SRR0603-150ML]	15 uH [SRR1210-150M]	15 uH [SRR6040A-150M]	15 uH [SRU3014-150Y]
15 uH [SRR0604-150ML]	15 uH [SRR1210A-150M]	15 uH [SRR6603-150ML]	15 uH [SRU3017-150Y]

Multisim 14.1 Education Components

15 uH [SRU3028-150Y]	15.4 kOhm [CR0603-FX-1542ELF]	15.8 kOhm [CR0805-FX-1582ELF]	150 kOhm [4116R-2-154LF]
15 uH [SRU3028A-150Y]	15.4 kOhm [CR0805-FX-1542ELF]	15.8 kOhm [CR1206-FX-1582ELF]	150 kOhm [4306R-101-154]
15 uH [SRU5011-150Y]	15.4 kOhm [CR1206-FX-1542ELF]	15.8 kOhm [CRT0603-BY-1582ELF]	150 kOhm [4306R-101-154LF]
15 uH [SRU5016-150Y]	15.4 kOhm [CRT0402-FZ-1542GLF]	15.8 kOhm [CRT1206-DY-1582ELF]	150 kOhm [4306R-102-154LF]
15 uH [SRU5018-150Y]	15.4 kOhm [CRT0805-BY-1542ELF]	15.8 Ohm [CR0805-FX-15R8ELF]	150 kOhm [4306R-102-154]
15 uH [SRU5028-150Y]	15.4 kOhm [CRT1206-BY-1542ELF]	15.8 Ohm [CR1206-FX-15R8ELF]	150 kOhm [4308M-102-154LF]
15 uH [SRU5028A-150Y]	15.4 kOhm [CRT1206-FZ-1542ELF]	15 AMP	150 kOhm [4308M-102-154LF]
15 uH [SRU6011-150Y]	15.4 kOhm [CR0402-FX-15R4GLF]	150 kOhm [4114R-1-154]	150 kOhm [4308R-101-154LF]
15 uH [SRU6018-150Y]	15.4 Ohm [CR0603-FX-15R4ELF]	150 kOhm [4114R-2-154]	150 kOhm [4308R-102-154]
15 uH [SRU6025-150Y]	15.4 Ohm [CR1206-FX-15R4ELF]	150 kOhm [4114R-2-154LF]	150 kOhm [4308R-102-154LF]
15 uH [SRU6025A-150Y]	15.8 kOhm [CR0402-FX-1582GLF]	150 kOhm [4116R-1-154]	150 kOhm [4309R-101-154]
15 uH [SRU8028-150Y]	15.8 kOhm [CR0603-FX-1582ELF]	150 kOhm [4116R-1-154LF]	150 kOhm [4309R-101-154LF]
15 uH [SRU8028A-150Y]	15.4 kOhm [CR0402-FX-1582GLF]	150 kOhm [4116R-2-154]	150 kOhm [4310H-102-154]
15 uH [SRU8043-150Y]	15.4 kOhm [CR0603-FX-1582ELF]	150 kOhm [4116R-2-154]	150 kOhm [4310R-101-154]
15.4 kOhm [CR0402-FX-1542GLF]			

Multisim 14.1 Education Components

150 kOhm [4310R-101-154LF]	150 kOhm [4610X-102-154LF]	150 kOhm [4816P-T02-154]	150 kOhm [CHV2010-JW-154ELF]
150 kOhm [4310R-102-154]	150 kOhm [4611X-101-154LF]	150 kOhm [4816P-T02-154LF]	150 kOhm [CR0402-FX-1503GLF]
150 kOhm [4310R-102-154LF]	150 kOhm [4612X-102-154LF]	150 kOhm [4820P-T02-154]	150 kOhm [CR0402-JW-154GLF]
150 kOhm [4604X-102-154LF]	150 kOhm [4814P-1-154]	150 kOhm [CAT16-1503F4LF]	150 kOhm [CR0603-FX-1503ELF]
150 kOhm [4606X-101-154LF]	150 kOhm [4814P-2-154]	150 kOhm [CAT16-1503F8LF]	150 kOhm [CR0603-JW-154ELF]
150 kOhm [4606X-102-154LF]	150 kOhm [4814P-2-154LF]	150 kOhm [CAT16-154J4LF]	150 kOhm [CR0805-FX-1503ELF]
150 kOhm [4606X-AP2-154LF]	150 kOhm [4814P-T01-154]	150 kOhm [CAT25-154JALF]	150 kOhm [CR0805-JW-154ELF]
150 kOhm [4607M-101-154LF]	150 kOhm [4814P-T02-154]	150 kOhm [CAY10-154J2LF]	150 kOhm [CR1206-FX-1503ELF]
150 kOhm [4608M-101-154LF]	150 kOhm [4814P-T02-154LF]	150 kOhm [CAY10-154J4LF]	150 kOhm [CR1206-JW-154ELF]
150 kOhm [4608X-101-154LF]	150 kOhm [4816P-1-154]	150 kOhm [CAY16-1503F4LF]	150 kOhm [CHV1206-FW-1503ELF]
150 kOhm [4608X-102-154LF]	150 kOhm [4816P-1-154LF]	150 kOhm [CAY16-154J4LF]	150 kOhm [CR2512-JW-154ELF]
150 kOhm [4608X-AP2-154LF]	150 kOhm [4816P-2-154]	150 kOhm [CAY16-154J8LF]	150 kOhm [CRM1206-FX-1503ELF]
150 kOhm [4609X-101-154LF]	150 kOhm [4816P-2-154LF]	150 kOhm [CHV1206-JW-154ELF]	
150 kOhm [4610H-102-154LF]	150 kOhm [4816P-T01-154]		
150 kOhm [4610X-101-154LF]	150 kOhm [4816P-T01-154LF]		

Multisim 14.1 Education Components

150 kOhm [CRM2512-JW-154ELF]	150 mOhm [CRL2010-JW-R150ELF]	150 mOhm [PWR221T-30-R150F]	150 nF [C0603C154K8RACTU]
150 kOhm [CRT0402-BY-1503GLF]	150 mOhm [CRL2512-FW-R150ELF]	150 mOhm [PWR2615NR150JE]	150 nF [C0603C154M3VACTU]
150 kOhm [CRT0805-BY-1503EAS]	150 mOhm [CRL2512-JW-R150ELF]	150 mOhm [PWR2615WR150J]	150 nF [C0603C154M4VACTU]
150 kOhm [CRT0805-BY-1503ELF]	150 mOhm [CRM1206-FX-R150ELF]	150 mOhm [PWR2615WR150JE]	150 nF [C0603C154M8VACTU]
150 mOhm [CRL0603-FW-R150ELF]	150 mOhm [CRM1206-JX-R150ELF]	150 mOhm [PWR4525WR150J]	150 nF [C0805C154K3RACTU]
150 mOhm [CRL0603-JW-R150ELF]	150 mOhm [CRM2010-FX-R150ELF]	150 mOhm [PWR6327WR150J]	150 nF [C0805C154K4RACTU]
150 mOhm [CRL0805-FW-R150ELF]	150 mOhm [CRM2512-FX-R150ELF]	150 mOhm [PWR6327WR150JE]	150 nF [C0805C154K5RACTU]
150 mOhm [CRL0805-JW-R150ELF]	150 mOhm [PWR163S-25-R150FE]	150 nF [06123C154KAT2W]	150 nF [C0805C154K8RACTU]
150 mOhm [CRL1206-FW-R150ELF]	150 mOhm [PWR1913WR150J]	150 nF [06125C154KAT2W]	150 nF [C0805C154M3VACTU]
150 mOhm [CRL1206-JW-R150ELF]	150 mOhm [PWR1913WR150JE]	150 nF [C0603C154K4RACTU]	150 nF [C1206C154K1RACTU]
150 mOhm [CRL2010-FW-R150ELF]	150 mOhm [PWR220T-35-R150F]	150 nF [C0603C154K5RACTU]	150 nF [C1206C154K2RACTU]

Multisim 14.1 Education Components

150 nF [C1206C154K3RACT U]	150 nF [C1210C154K5RACT U]	150 nF [C1812C154K5RACT U]	150 nF [C2225C154K1RACT U]
150 nF [C1206C154K4RACT U]	150 nF [C1210F154K1RACT U]	150 nF [C1812C154M1UAC TU]	150 nF [C2225C154K2RACT U]
150 nF [C1206C154K5RACT U]	150 nF [C1210F154K3RACT U]	150 nF [C1812C154M5UAC TU]	150 nF [GMC5.7154K50J35 TR12]
150 nF [C1206C154M5UAC TU]	150 nF [C1210F154K4RACT U]	150 nF [C1812F154K1RACT U]	150 nF [GMC7.3154K63K31 TR12]
150 nF [C1206F154K1RACT U]	150 nF [C1210F154K5RACT U]	150 nF [C1812F154K2RACT U]	150 nF [MDC10154K100A5 2P3TUBE]
150 nF [C1206F154K3RACT U]	150 nF [C1812C154K1GACT U]	150 nF [C1812F154K3RACT U]	150 nF [MDC10154K250A5 2P3TUBE]
150 nF [C1206F154K4RACT U]	150 nF [C1812C154K1HACT U]	150 nF [C1812F154K5RACT U]	150 nF [MDC10154K400A5 2P3TUBE]
150 nF [C1206F154K5RACT U]	150 nF [C1812C154K1RACT U]	150 nF [C1825C154K1RACT U]	150 nF [MDC10154K50A52 P3TUBE]
150 nF [C1210C154K1RACT U]	150 nF [C1812C154K2RACT U]	150 nF [C1825C154K5RACT U]	150 nF [MDC10154K630A5 8P7TUBE]
150 nF [C1210C154K3HACT U]	150 nF [C1812C154K5GACT U]	150 nF [C2220C154K1GACT U]	150 nF [MDC10154K630A5 8P8TUBE]
150 nF [C1210C154K5HACT U]	150 nF [C1812C154K5HACT U]	150 nF [C2220C154K5GACT U]	150 nF [MDC15154K100B5 3P3TUBE]

Multisim 14.1 Education Components

150 nF [MDC15154K250B5 3P3TUBE]	150 nF [MDS10154K50A52 P3TUBE]	150 nF [T494A154M035AT]	150 nH [SRP7030- R15FM]
150 nF [MDC15154K400B5 3P3TUBE]	150 nF [MDS15154K100B5 3P3TUBE]	150 nF [T494A154M050AT]	150 Ohm [4108R-1- 151LF]
150 nF [MDC15154K50B53 P3TUBE]	150 nF [MDS15154K250B5 3P3TUBE]	150 nF [T494B154M050AT]	150 Ohm [4114R-1- 151]
150 nF [MDK10154K100A5 2P3TUBE]	150 nF [MDS15154K250B5 3P3TUBE]	150 nF [TAJA154K035RNJ]	150 Ohm [4114R-1- 151LF]
150 nF [MDK10154K250A5 2P3TUBE]	150 nF [MMC5.7154K50J3 3TR12]	150 nF [TAJA154K050RNJ]	150 Ohm [4114R-2- 151]
150 nF [MDK10154K250A5 2P3TUBE]	150 nF [MMC7.3154K50K3 1TR12]	150 nF [TAJB154K050RNJ]	150 Ohm [4114R-2- 151LF]
150 nF [MDK10154K400A5 2P3TUBE]	150 nF [MMC7.3154K50K3 1TR12]	150 nF [TAJR154K020RNJ]	150 Ohm [4116R-1- 151]
150 nF [MDK10154K400A5 2P3TUBE]	150 nF [SPC12.7154K100B 31TR24]	150 nF [TAJS154K020RNJ]	150 Ohm [4116R-1- 151LF]
150 nF [MDK10154K50A52 P3TUBE]	150 nF [SPC12.7154K100B 31TR24]	150 nF [TAJS154K035RNJ]	150 Ohm [4116R-2- 151]
150 nF [MDK15154K400B5 3P3TUBE]	150 nF [SPC16.5154K250C 31TR24]	150 nF [THJA154K035RJN]	150 Ohm [4116R-2- 151LF]
150 nF [MDK15154K400B5 3P3TUBE]	150 nF [SPC16.5154K400C 31TR24]	150 nF [TPSA154K050R900 0]	150 Ohm [4304M- 102-151]
150 nF [MDS10154K100A5 2P3TUBE]	150 nF [T429A154M050AH 4250]	150 nF [TRJA154K035RRJ]	150 Ohm [4306M- 101-151]
150 nF [MDS10154K250A5 2P3TUBE]	150 nF [T491A154M035AT]	150 nH [SRP1040- R15M]	150 Ohm [4306M- 101-151LF]
150 nF [MDS10154K400A5 2P3TUBE]	150 nF [T491A154M050AT]	150 nH [SRP1235- R15M]	150 Ohm [4306R- 101-151]
	150 nF [T491B154M050AT]	150 nH [SRP5015TA-R15Y]	150 Ohm [4306R- 101-151LF]

Multisim 14.1 Education Components

150 Ohm [4306R-102-151]	150 Ohm [4310R-101-151]	150 Ohm [4606H-101-151LF]	150 Ohm [4610X-101-151LF]
150 Ohm [4306R-102-151LF]	150 Ohm [4310R-101-151LF]	150 Ohm [4606H-102-151LF]	150 Ohm [4610X-102-151LF]
150 Ohm [4308H-101-151]	150 Ohm [4310R-102-151]	150 Ohm [4606X-101-151LF]	150 Ohm [4610X-AP2-151LF]
150 Ohm [4308H-102-151]	150 Ohm [4310R-102-151LF]	150 Ohm [4606X-102-151LF]	150 Ohm [4612X-101-151LF]
150 Ohm [4308M-101-151]	150 Ohm [4416P-1-151]	150 Ohm [4607M-101-151LF]	150 Ohm [4612X-102-151LF]
150 Ohm [4308R-101-151]	150 Ohm [4416P-2-151]	150 Ohm [4607X-101-151LF]	150 Ohm [4614X-102-151LF]
150 Ohm [4308R-101-151LF]	150 Ohm [4416P-T01-151]	150 Ohm [4608M-101-151LF]	150 Ohm [4814P-1-151]
150 Ohm [4308R-102-151]	150 Ohm [4416P-T02-151]	150 Ohm [4608M-102-151LF]	150 Ohm [4814P-1-151LF]
150 Ohm [4308R-102-151LF]	150 Ohm [4420P-1-151]	150 Ohm [4608X-101-151LF]	150 Ohm [4814P-2-151]
150 Ohm [4309R-101-151]	150 Ohm [4420P-2-151]	150 Ohm [4608X-102-151LF]	150 Ohm [4814P-2-151LF]
150 Ohm [4309R-101-151LF]	150 Ohm [4420P-T01-151]	150 Ohm [4608X-AP2-151LF]	150 Ohm [4814P-T01-151]
150 Ohm [4310H-101-151]	150 Ohm [4420P-T02-151]	150 Ohm [4609M-101-151LF]	150 Ohm [4814P-T01-151LF]
150 Ohm [4310H-101-151LF]	150 Ohm [4604X-101-151LF]	150 Ohm [4609X-101-151LF]	150 Ohm [4814P-T02-151]
150 Ohm [4310H-102-151]	150 Ohm [4604X-102-151LF]	150 Ohm [4609X-AP1-151LF]	150 Ohm [4814P-T02-151LF]
150 Ohm [4310M-101-151]	150 Ohm [4605X-101-151LF]	150 Ohm [4610M-101-151LF]	150 Ohm [4816P-1-151]

Multisim 14.1 Education Components

150 Ohm [4816P-1-151LF]	150 Ohm [CAT16-151J4LF]	150 Ohm [CR0805-FX-1500ELF]	150 Ohm [CRM2512-JW-151ELF]
150 Ohm [4816P-2-151]	150 Ohm [CAT16-151J8LF]	150 Ohm [CR0805-FX-1500GLF]	150 Ohm [CRT0603-BY-1500ELF]
150 Ohm [4816P-2-151LF]	150 Ohm [CAT25-151JALF]	150 Ohm [CR0805-JW-151ELF]	150 Ohm [CRT0805-BY-1500ELF]
150 Ohm [4816P-T01-151]	150 Ohm [CAY10-151J4LF]	150 Ohm [CR1206-FX-1500ELF]	150 Ohm [CRT0805-DY-1500ELF]
150 Ohm [4816P-T01-151LF]	150 Ohm [CAY16-1500F4LF]	150 Ohm [CR1206-JW-151ELF]	150 Ohm [PWR163S-25-1500FE]
150 Ohm [4816P-T02-151]	150 Ohm [CAY16-151J4LF]	150 Ohm [CR2010-FX-1500ELF]	150 Ohm [PWR220T-20-1500F]
150 Ohm [4816P-T02-151LF]	150 Ohm [CAY16-151J8LF]	150 Ohm [CR2010-JW-151ELF]	150 Ohm [PWR220T-35-1500F]
150 Ohm [4818P-T02-151]	150 Ohm [CAY17-151JALF]	150 Ohm [CR2512-FX-1500ELF]	150 Ohm [PWR221T-30-1500F]
150 Ohm [4818P-T02-151LF]	150 Ohm [CR0201-FW-1500GLF]	150 Ohm [CR2512-JW-151ELF]	150 Ohm [PWR2615W1500J]
150 Ohm [4820P-1-151]	150 Ohm [CR0402-FX-1500GLF]	150 Ohm [CRM1206-FX-1500ELF]	150 Ohm [PWR2615W1500JE]
150 Ohm [4820P-T01-151]	150 Ohm [CR0402-JW-151GLF]	150 Ohm [CRM2010-FX-1500ELF]	
150 Ohm [4820P-T02-151]	150 Ohm [CR0603-FX-1500ELF]	150 Ohm [CRM2010-JW-151ELF]	
150 Ohm [CAT10-151J4LF]	150 Ohm [CR0603-FX-1500HLF]	150 Ohm [CRM2512-FX-1500ELF]	
150 Ohm [CAT16-1500F4LF]	150 Ohm [CR0603-JW-151ELF]		
150 Ohm [CAT16-1500F8LF]	150 Ohm [CR0603-JW-151GLF]		

Multisim 14.1 Education Components

150 Ohm [PWR263S-35-1500FE]	150 pF [C0402C151K4RACTU]	150 pF [C0805C151K3GACTU]	150 pF [C2225C151KBGAC TU]
150 Ohm [PWR263S-35-1500J]	150 pF [C0402C151K5GACTU]	150 pF [C0805C151K4GACTU]	150 pF [CA064C151K4GAC TU]
150 Ohm [PWR4525W1500J]	150 pF [C0402C151K5HACTU]	150 pF [C0805C151K5GACTU]	150 pF [CA064C151K5GAC TU]
150 Ohm [PWR4525W1500JE]]	150 pF [C0402C151K5RACTU]	150 pF [C1206C151K1GACTU]	150 uF [10TPB150ML]
150 Ohm [PWR5322W1500JE]]	150 pF [C0402C151K8RACTU]	150 pF [C1206C151K2GACTU]	150 uF [10TPF150ML]
150 Ohm [PWR6327W1500J]	150 pF [C0603C151K1GACTU]	150 pF [C1206C151K5GACTU]	150 uF [16TQC150MYF]
150 Ohm [PWR6327W1500JE]]	150 pF [C0603C151K3GACTU]	150 pF [C1206C151KBGAC TU]	150 uF [4SVPC150MY]
150 Ohm [WS1M1500J]	150 pF [C0603C151K4GACTU]	150 pF [C1210C151KBGAC TU]	150 uF [4TPE150MAZB]
150 Ohm [WS2M1500J]	150 pF [C0603C151K5GACTU]	150 pF [C1812C151KBGAC TU]	150 uF [4TPH150MABC]
150 pF [C0402C151K1HACTU]	150 pF [C0805C151K1GACTU]	150 pF [C1825C151KBGAC TU]	150 uF [6SVPE150M]
150 pF [C0402C151K3HACTU]	150 pF [C0805C151K2GACTU]	150 pF [C2220C151KBGAC TU]	150 uF [6TPC150M]
150 pF [C0402C151K3RACTU]			150 uF [6TPE150M]
			150 uF [6TPE150MAPB]

Multisim 14.1 Education Components

150 uF [6TPE150MAZB]	150 uF [A700V157M002AT E025]	150 uF [EEHZA1V151P]	150 uF [T491V157M006AT]
150 uF [6TPE150MF]	150 uF [A700V157M002AT E028]	150 uF [EEHZC1V151P]	150 uF [T491V157M010AT]
150 uF [6TPE150MI]	150 uF [A700X157M006AT E010]	150 uF [T429G157M006AH 4250]	150 uF [T491X157M010AT]
150 uF [6TPG150M]	150 uF [A700X157M006AT E015]	150 uF [T429X157M010AH 4250]	150 uF [T491X157M016AT]
150 uF [6TPG150MZG]	150 uF [A700X157M010AT E010]	150 uF [T491B157M004AT]	150 uF [T491X157M020AT]
150 uF [6TPU150MBI]	150 uF [A700D157M004AT E015]	150 uF [T491C157M004AT]	150 uF [T494B157M004AT]
150 uF [8TPC150M]	150 uF [A700D157M004AT E018]	150 uF [T491C157M006AT]	150 uF [T494C157M004AT]
150 uF [A700D157M2R5AT E015]	150 uF [EEFCX0G151R]	150 uF [T491C157M010AT]	150 uF [T494C157M006AT]
150 uF [A700D157M2R5AT E018]	150 uF [EEFCX0J151R]	150 uF [T491D157M004AT]	150 uF [T494C157M010AT]
150 uF [A700D157M2R5AT E015]	150 uF [EEFCX0J151XR]	150 uF [T491D157M006AT]	150 uF [T494D157M004AT]
150 uF [A700D157M2R5AT E018]	150 uF [EEFSX0E151ER]	150 uF [T491D157M010AT]	150 uF [T494D157M006AT]
150 uF [A700V157M002AT E009]	150 uF [EEFSX0G151E7]	150 uF [T491D157M016AT]	150 uF [T494D157M010AT]
150 uF [A700V157M002AT E018]	150 uF [EEFSX0G151ER]	150 uF [T491V157M004AT]	150 uF [T494D157M016AT]
			150 uF [T494V157M004AT]

Multisim 14.1 Education Components

150 uF [T494V157M006AT]	150 uF [T495D157M016AT E060]	150 uF [T510X157M016AT E040]	150 uF [T520B157M004AT E035]
150 uF [T494V157M010AT]	150 uF [T495D157M016AT E085]	150 uF [T513X157M016AH 6110]	150 uF [T520B157M004AT E040]
150 uF [T494X157M010AT]	150 uF [T495D157M016AT E100]	150 uF [T513X157M016AH 6120]	150 uF [T520B157M004AT E070]
150 uF [T494X157M020AT]	150 uF [T495D157M016AT E125]	150 uF [T520B157M003AT E025]	150 uF [T520B157M006AT E035]
150 uF [T495B157M004AT E900]	150 uF [T495D157M016AT E150]	150 uF [T520B157M003AT E035]	150 uF [T520B157M006AT E045]
150 uF [T495C157M006AT E200]	150 uF [T495V157M010AT E150]	150 uF [T520B157M003AT E040]	150 uF [T520B157M006AT E070]
150 uF [T495D157M006AT E050]	150 uF [T495X157M010AT E085]	150 uF [T520B157M003AT E070]	150 uF [T520C157M004AT E015]
150 uF [T495D157M006AT E125]	150 uF [T495X157M010AT E100]	150 uF [T520B157M004AT E015]	150 uF [T520C157M004AT E025]
150 uF [T495D157M010AT E050]	150 uF [T495X157M016AT E075]	150 uF [T520B157M004AT E018]	150 uF [T520C157M004AT E045]
150 uF [T495D157M010AT E060]	150 uF [T495X157M016AT E100]	150 uF [T520B157M004AT E025]	150 uF [T520C157M004AT E100]
150 uF [T495D157M010AT E100]	150 uF [T510X157M016AT E030]	150 uF [T520B157M004AT E030]	150 uF [T520C157M006AT E015]

Multisim 14.1 Education Components

150 uF [T520C157M006AT E025]	150 uF [T520D157M008AT E040]	150 uF [T520U157M2R5AT E055]	150 uF [T520V157M006AT E018]
150 uF [T520C157M006AT E045]	150 uF [T520D157M008AT E055]	150 uF [T520V157M004AT E007]	150 uF [T520V157M006AT E025]
150 uF [T520C157M006AT E055]	150 uF [T520D157M010AT E025]	150 uF [T520V157M004AT E009]	150 uF [T520V157M006AT E040]
150 uF [T520C157M010AT E055]	150 uF [T520D157M010AT E040]	150 uF [T520V157M004AT E012]	150 uF [T520V157M006AT E045]
150 uF [T520D157M004AT E007]	150 uF [T520D157M010AT E055]	150 uF [T520V157M004AT E015]	150 uF [T520V157M010AT E018]
150 uF [T520D157M006AT E006]	150 uF [T520L157M006AT E012]	150 uF [T520V157M004AT E025]	150 uF [T520V157M010AT E040]
150 uF [T520D157M006AT E007]	150 uF [T520L157M006AT E025]	150 uF [T520V157M006AT E006]	150 uF [T520W157M006AT E025]
150 uF [T520D157M006AT E015]	150 uF [T520M157M006AT E070]	150 uF [T520V157M006AT E007]	150 uF [T520W157M006AT E040]
150 uF [T520D157M006AT E025]	150 uF [T520U157M004AT E055]	150 uF [T520V157M006AT E009]	150 uF [T520X157M016AT E040]
150 uF [T520D157M006AT E055]	150 uF [T520U157M006AT E045]	150 uF [T520V157M006AT E012]	150 uF [T522V157M006AT E040]
150 uF [T520D157M008AT E025]	150 uF [T520U157M006AT E055]	150 uF [T520V157M006AT E015]	150 uF [T525B157M003AT E080]

Multisim 14.1 Education Components

150 uF [T525D157M006AT E025]	150 uF [TAJB157K002RNJ]	150 uF [TAJY157K010RNJ]	150 uF [TPSD157K006R012 5]
150 uF [T525D157M010AT E025]	150 uF [TAJB157K004RNJ]	150 uF [THJD157K006RJN]	150 uF [TPSD157K010R005 0]
150 uF [T528Z157M006AT E007]	150 uF [TAJC157K006RNJ]	150 uF [TPME157K016R00 30]	150 uF [TPSD157K010R008 5]
150 uF [T528Z157M006AT E008]	150 uF [TAJD157K006RNJ]	150 uF [TPME157K016R00 40]	150 uF [TPSD157K010R010 0]
150 uF [T528Z157M006AT E009]	150 uF [TAJD157K010RNJ]	150 uF [TPME157K020R00 35]	150 uF [TPSD157K016R010 0]
150 uF [T528Z157M006AT E012]	150 uF [TAJE157K010RNJ]	150 uF [TPSB157K002R015 0]	150 uF [TPSD157K016R012 5]
150 uF [T530D157M010AT E006]	150 uF [TAJE157K016RNJ]	150 uF [TPSC157K006R005 0]	150 uF [TPSD157K016R015 0]
150 uF [T530D157M010AT E010]	150 uF [TAJE157K020RNJ]	150 uF [TPSC157K006R009 0]	150 uF [TPSE157K016R010 0]
150 uF [T530X157M016AT E015]	150 uF [TAJF157K010RNJ]	150 uF [TPSC157K006R015 0]	150 uF [TPSV157K016R004 5]
150 uF [T530X157M016AT E025]	150 uF [TAJV157K016RNJ]	150 uF [TPSC157K006R020 0]	150 uF [TPSV157K016R007 5]
150 uF [T530X157M016AT E040]	150 uF [TAJX157K006RNJ]	150 uF [TPSC157K006R025 0]	150 uF [TPSV157K020R008 0]
	150 uF [TAJY157K006RNJ]	150 uF [TPSD157K006R005 0]	

Multisim 14.1 Education Components

150 uF [TPSY157K006R004 0]	150 uH [SDR0302- 151KL]	150 uH [SDR1307A-151K]	150 uH [SRR0906- 151YL]
150 uF [TPSY157K010R010 0]	150 uH [SDR0403- 151KL]	150 uH [SDR1806- 151KL]	150 uH [SRR0908- 151YL]
150 uF [TPSY157K010R015 0]	150 uH [SDR0503- 151KL]	150 uH [SDR6603- 151M]	150 uH [SRR1003- 151M]
150 uF [TPSY157K010R015 0]	150 uH [SDR0603- 151KL]	150 uH [SDR7030- 151K]	150 uH [SRR1005- 151K]
150 uF [TPSY157K010R020 0]	150 uH [SDR0604- 151KL]	150 uH [SDR7045- 151K]	150 uH [SRR1205- 151KL]
150 uF [TRJC157K006RRJ]	150 uH [SDR0703- 151KL]	150 uH [SRN1060- 151M]	150 uH [SRR1206- 151KL]
150 uF [TRJD157K010RRJ]	150 uH [SDR0805- 151KL]	150 uH [SRN4018- 151M]	150 uH [SRR1208- 151YL]
150 uF [TRJE157K010RRJ]	150 uH [SDR0906- 151KL]	150 uH [SRN4026- 151M]	150 uH [SRR1210- 151M]
150 uF [TRJE157K016RRJ]	150 uH [SDR1005- 151KL]	150 uH [SRR0603- 151KL]	150 uH [SRR1210A- 151M]
150 uF [TRME157K016R00 30]	150 uH [SDR1006- 151KL]	150 uH [SRR0604- 151KL]	150 uH [SRR1240- 151K]
150 uF [TRME157K016R00 30]	150 uH [SDR1030- 151K]	150 uH [SRR0735A- 151M]	150 uH [SRR1260- 151K]
150 uF [TRME157K016R00 40]	150 uH [SDR1045- 151K]	150 uH [SRR0745A- 151M]	150 uH [SRR1260A- 151K]
150 uH [SDE0604A- 151K]	150 uH [SDR1105- 151KL]	150 uH [SRR0804- 151K]	150 uH [SRR1280- 151K]
150 uH [SDE0805A- 151K]	150 uH [SDR1305- 151K]	150 uH [SRR0805- 151K]	150 uH [SRR1806- 151M]
150 uH [SDE1006A- 151K]	150 uH [SDR1307- 151KL]	150 uH [SRR0905- 151K]	150 uH [SRR4011- 151YL]

Multisim 14.1 Education Components

150 uH [SRR4018-151Y]	150 uH [SRU6025A-151Y]	158 kOhm [CR0402-FX-1583GLF]	16 kOhm [CAT16-163J4LF]
150 uH [SRR4028-151Y]	1-534206-0	158 kOhm [CR0603-FX-1583ELF]	16 kOhm [CAY16-163J4LF]
150 uH [SRR5018-151Y]	1-534206-3		
	1-534206-7		
150 uH [SRR5028-151Y]	154 kOhm [CR0402-FX-1543GLF]	158 kOhm [CR0603-FX-1583GLF]	16 kOhm [CR0402-FX-1602GLF]
150 uH [SRR6028-151Y]	154 kOhm [CR0603-FX-1543ELF]	158 kOhm [CR0805-FX-1583ELF]	16 kOhm [CR0603-JW-163ELF]
150 uH [SRR6603-151ML]	154 kOhm [CR0805-FX-1543ELF]	158 kOhm [CR1206-FX-1583ELF]	16 kOhm [CR0805-FX-1602ELF]
150 uH [SRR7032-151M]	154 kOhm [CR1206-FX-1543ELF]	158 kOhm [CRT0805-BY-1583ELF]	16 kOhm [CR0805-JW-163ELF]
150 uH [SRR7045-151M]	154 kOhm [CRT1206-BY-1543ELF]		
150 uH [SRU1028-151Y]	154 kOhm [CRT1206-FZ-1543ELF]	158 Ohm [CR0603-FX-1580ELF]	16 kOhm [CR1206-JW-163ELF]
150 uH [SRU1028A-151Y]	154 kOhm [CR0402-FX-1540GLF]	158 Ohm [CR0805-FX-1580ELF]	16 kOhm [CRT0402-BY-1602GLF]
150 uH [SRU1038-151Y]	154 Ohm [CR0603-FX-1540ELF]	158 Ohm [CR1206-FX-1580ELF]	16 kOhm [CRT0402-BZ-1602GLF]
150 uH [SRU1038A-151Y]		15C02MH-TL-E	
150 uH [SRU1048-151Y]	154 Ohm [CR0805-FX-1540ELF]	15CGQ100	16 Ohm [CAT10-160J4LF]
150 uH [SRU1048A-151Y]		15CLQ100	
150 uH [SRU6025-151Y]	154 Ohm [4116R-1-163]	15LJQ100	16 Ohm [CAT16-160J4LF]
	154 Ohm [4604X-102-163LF]		16 Ohm [CAT16-160J8LF]
			16 Ohm [CAY16-160J4LF]

Multisim 14.1 Education Components

16 Ohm [CR0402-FX-16R0GLF]	16 pF [C1210C160KBGAC TU]	16.2 kOhm [CRT0402-FZ-1622GLF]	16.5 Ohm [CR0402-FX-16R5GLF]
16 Ohm [CR0603-FX-16R0ELF]	16 pF [C1812C160KBGAC TU]	16.2 kOhm [CRT0603-BY-1622ELF]	16.5 Ohm [CR0603-FX-16R5ELF]
16 Ohm [CR0603-JW-160ELF]	16 pF [C1825C160KBGAC TU]	16.2 Ohm [CR0402-FX-16R2GLF]	16.5 Ohm [CR0805-FX-16R5ELF]
16 Ohm [CR0805-JW-160ELF]	16 pF [C2220C160KBGAC TU]	16.2 Ohm [CR0603-FX-16R2ELF]	16.5 Ohm [CR1206-FX-16R5ELF]
16 Ohm [CR1206-FX-16R0ELF]	16 pF [C2225C160KBGAC TU]	16.2 Ohm [CR0805-FX-16R2ELF]	16.9 kOhm [CR0402-FX-1692GLF]
16 Ohm [CR1206-JW-160ELF]	16.2 kOhm [CAY16-1622F4LF]	16.2 Ohm [CR1206-FX-16R2ELF]	16.9 kOhm [CR0603-FX-1692ELF]
16 Ohm [CRM2512-JW-160ELF]	16.2 kOhm [CR0402-FX-1622GLF]	16.2 Ohm [CRT0402-FZ-16R2GLF]	16.9 kOhm [CR0805-FX-1692ELF]
16 Ohm [CRT0805-BW-16R0ELF]	16.2 kOhm [CR0603-FX-1622ELF]	16.5 kOhm [CR0402-FX-1652GLF]	16.9 kOhm [CR1206-FX-1692ELF]
16 pF [C0603C160K2GACT U]	16.2 kOhm [CR0805-FX-1622ELF]	16.5 kOhm [CR0603-FX-1652ELF]	16.9 kOhm [CRT0603-BY-1692ELF]
16 pF [C0603C160K5GACT U]	16.2 kOhm [CR1206-FX-1622ELF]	16.5 kOhm [CR0805-FX-1652ELF]	16.9 kOhm [CRT0805-BY-1692ELF]
16 pF [C0805C160KBGAC TU]	16.2 kOhm [CRM2010-FX-1622ELF]	16.5 kOhm [CR1206-FX-1652ELF]	16.9 kOhm [CRT1206-BY-1692ELF]
16 pF [C1206C160KBGAC TU]		16.5 kOhm [CRT0805-CX-1652ELF]	16.9 Ohm [CR0402-FX-16R9GLF]
			16.9 Ohm [CR0603-FX-16R9ELF]

Multisim 14.1 Education Components

16.9 Ohm [CR0805-FX-16R9ELF]	160 kOhm [CRT0805-BY-1603ELF]	160 mOhm [CRM1206-FX-R160ELF]	160 Ohm [CAY16-1600F4LF]
16.9 Ohm [CR1206-FX-16R9ELF]	160 mOhm [CRL0603-FW-R160ELF]	160 mOhm [CRM1206-JX-R160ELF]	160 Ohm [CAY16-161J4LF]
160 kOhm [CAT16-1603F4LF]	160 mOhm [CRL0603-JW-R160ELF]	160 Ohm [4114R-1-161]	160 Ohm [CAY16-161J8LF]
160 kOhm [CAY16-164J4LF]	160 mOhm [CRL0805-FW-R160ELF]	160 Ohm [4114R-1-161LF]	160 Ohm [CR0402-FX-1600GLF]
160 kOhm [CR0402-FX-1603GLF]	160 mOhm [CRL0805-JW-R160ELF]	160 Ohm [4306R-101-161]	160 Ohm [CR0603-FX-1600ELF]
160 kOhm [CR0603-FX-1603ELF]	160 mOhm [CRL1206-FW-R160ELF]	160 Ohm [4306R-101-161LF]	160 Ohm [CR0603-JW-161ELF]
160 kOhm [CR0603-JW-164ELF]	160 mOhm [CRL1206-JW-R160ELF]	160 Ohm [4308R-101-161]	160 Ohm [CR0805-FX-1600ELF]
160 kOhm [CR0805-FX-1603ELF]	160 mOhm [CRL2010-FW-R160ELF]	160 Ohm [4310R-101-161]	160 Ohm [CR0805-JW-161ELF]
160 kOhm [CR0805-JW-164ELF]	160 mOhm [CRL2010-JW-R160ELF]	160 Ohm [4310R-101-161LF]	160 Ohm [CR1206-FX-1600ELF]
160 kOhm [CR1206-FX-1603ELF]	160 mOhm [CRL2512-FW-R160ELF]	160 Ohm [4814P-2-161]	160 Ohm [CR1206-JW-161ELF]
160 kOhm [CR1206-JW-164ELF]	160 mOhm [CRL2512-JW-R160ELF]	160 Ohm [4820P-1-161]	160 Ohm [CRM1206-JW-161ELF]
160 kOhm [CRT0402-BY-1603GLF]	160 mOhm [CRL2512-JW-R160ELF]	160 Ohm [CAT16-161J4LF]	160 Ohm [CRT0805-CX-1600ELF]
		160 Ohm [CAT16-161J8LF]	160 pF [C0402C161K1HACT U]
		160 Ohm [CAT25-161JALF]	160 pF [C0402C161K3HACT U]
		160 Ohm [CAY10-161J4LF]	

Multisim 14.1 Education Components

160 pF [C0402C161K5HACT U]	162 kOhm [CR0603-FX- 1623ELF]	162 Ohm [PWR5322W1620FE]	169 kOhm [CR0805-FX- 1693ELF]
160 pF [C0805C161K3GACT U]	162 kOhm [CR0805-FX- 1623ELF]	1-640455-0 165 kOhm [CR0402-FX- 1653GLF]	169 kOhm [CR1206-FX- 1693ELF]
160 pF [C0805C161K5GACT U]	162 kOhm [CR1206-FX- 1623ELF]	165 kOhm [CR0603-FX- 1653ELF]	169 kOhm [CRT0805-BY- 1693ELF]
160 pF [C1206C161KBGAC TU]	162 kOhm [CRT0603-BY- 1623ELF]	165 kOhm [CR0805-FX- 1653ELF]	169 Ohm [CAT16- 1690F4LF]
160 pF [C1210C161KBGAC TU]	162 kOhm [CRT0805-BY- 1623ELF]	165 kOhm [CR1206-FX- 1653ELF]	169 Ohm [CR0402- FX-1690GLF]
160 pF [C1812C161KBGAC TU]	162 Ohm [CAT16- 1620F4LF]	165 Ohm [CAT16- 1650F4LF]	169 Ohm [CR0805- FX-1690ELF]
160 pF [C1825C161KBGAC TU]	162 Ohm [CR0402- FX-1620GLF]	165 Ohm [CR0402- FX-1650GLF]	169 Ohm [CR1206- FX-1690ELF]
160 pF [C2220C161KBGAC TU]	162 Ohm [CR0603- FX-1620ELF]	165 Ohm [CR0603- FX-1650ELF]	16CYQ100C
160 pF [C2225C161KBGAC TU]	162 Ohm [CR0805- FX-1620ELF]	165 Ohm [CR0805- FX-1650ELF]	16CYQ150C
160 pF [C2225C161KBGAC TU]	162 Ohm [CR1206- FX-1620ELF]	165 Ohm [CR1206- FX-1650ELF]	16SYQ060C
162 kOhm [CAT16- 1623F4LF]	162 Ohm [CRT0402-FZ- 1620GLF]	169 kOhm [CR0402-FX- 1693GLF]	16YQ045C
162 kOhm [CR0402-FX- 1623GLF]	162 Ohm [CRT0805-BY- 1620ELF]	169 kOhm [CR0603-FX- 1693ELF]	16YQ150C
			17 mOhm [CRA2512-JZ- R017ELF]
			17.4 kOhm [CR0402-FX- 1742GLF]

Multisim 14.1 Education Components

178 kOhm [CR0402-FX- 1783GLF]	178 Ohm [CR1206- FX-1780ELF]	18 kOhm [4116R-2- 183]	18 kOhm [4310M- 101-183LF]
178 kOhm [CR0603-FX- 1783ELF]	178 Ohm [CRT0402-FZ- 1780GLF]	18 kOhm [4116R-2- 183LF]	18 kOhm [4310R- 101-183]
178 kOhm [CR0603-FX- 1783GLF]	178 Ohm [CRT0805-DZ- 1780ELF]	18 kOhm [4306R- 101-183]	18 kOhm [4310R- 101-183LF]
178 kOhm [CR0805-FX- 1783ELF]	1786837	18 kOhm [4306R- 102-183]	18 kOhm [4310R- 102-183LF]
178 kOhm [CR1206-FX- 1783ELF]	1786866	18 kOhm [4306R- 102-183LF]	18 kOhm [4416P-1- 183]
178 kOhm [CR2512-FX- 1783ELF]	1786918	18 kOhm [4308H- 101-183]	18 kOhm [4605X- 101-183LF]
178 kOhm [CRT0805-BY- 1783ELF]	1786963	18 kOhm [4308H- 102-183]	18 kOhm [4606X- 101-183LF]
178 kOhm [CRT1206-DX- 1783ELF]	1787205	18 kOhm [4308H- 102-183LF]	18 kOhm [4606X- 102-183LF]
178 Ohm [CR0402- FX-1780GLF]	1787234	18 kOhm [4308M- 102-183]	18 kOhm [4608M- 102-183LF]
178 Ohm [CR0603- FX-1780ELF]	1787289	18 kOhm [4308R- 101-183]	18 kOhm [4608X- 101-183LF]
178 Ohm [CR0805- FX-1780ELF]	1787331	18 kOhm [4308R- 101-183LF]	18 kOhm [4609X- 101-183LF]
178 Ohm [CR0805- FX-1780GLF]	1787386	18 kOhm [4308R- 102-183LF]	18 kOhm [4610X- 101-183LF]
	1787580	18 kOhm [4310M- 101-183]	18 kOhm [4610X- 102-183LF]
	18 kOhm [4114R-1- 183]		
	18 kOhm [4114R-2- 183]		
	18 kOhm [4116R-1- 183]		
	18 kOhm [4116R-1- 183LF]		

Multisim 14.1 Education Components

18 kOhm [4814P-2-183]	18 kOhm [CAT25-183JALF]	18 kOhm [CR2010-JW-183ELF]	18 nF [C0402C183K8RACTU]
18 kOhm [4814P-2-183LF]	18 kOhm [CAY16-1802F4LF]	18 kOhm [CR2512-JW-183ELF]	18 nF [C0402C183K9PACTU]
18 kOhm [4816P-1-183]	18 kOhm [CAY16-183J4LF]	18 kOhm [CRM1206-JW-183ELF]	18 nF [C0402C183K9RACTU]
18 kOhm [4816P-1-183LF]	18 kOhm [CAY16-183J8LF]	18 kOhm [CRT0603-DY-1802ELF]	18 nF [C0603C183K1RACTU]
18 kOhm [4816P-2-183]	18 kOhm [CAY17-183JALF]	18 kOhm [CRT0805-BY-1802ELF]	18 nF [C0603C183K3RACTU]
18 kOhm [4816P-2-183LF]	18 kOhm [CR0402-FX-1802GLF]	18 kOhm [CRT1206-BY-1802ELF]	18 nF [C0603C183K4RACTU]
18 kOhm [4816P-T01-183]	18 kOhm [CR0402-JW-183GLF]	18 kOhm [PWR163S-25-1802FE]	18 nF [C0603C183K5RACTU]
18 kOhm [4816P-T01-183LF]	18 kOhm [CR0603-FX-1802ELF]	18 kOhm [PWR263S-35-1802JE]	18 nF [C0603C183K8RACTU]
18 kOhm [4816P-T02-183]	18 kOhm [CR0603-JW-183GLF]	18 MOhm [CHV0805-JW-186ELF]	18 nF [C0805C183K1RACTU]
18 kOhm [4816P-T02-183LF]	18 kOhm [CR0805-FX-1802ELF]	18 mOhm [CRF2512-FZ-R018ELF]	18 nF [C0805C183K3GACTU]
18 kOhm [4820P-2-183]	18 kOhm [CR0805-JW-183ELF]	18 nF [C0402C183K4RACTU]	18 nF [C0805C183K3HACTU]
18 kOhm [4820P-T01-183]	18 kOhm [CR0805-JW-183GLF]	18 nF [C0402C183K8PACTU]	
18 kOhm [4820P-T02-183]	18 kOhm [CR1206-FX-1802ELF]		
18 kOhm [CAT16-1802F4LF]	18 kOhm [CR1206-JW-183ELF]		
18 kOhm [CAT16-183J4LF]			

Multisim 14.1 Education Components

18 nF [C0805C183K4RACT U]	18 nF [C1206C183K2RACT U]	18 nF [C1210C183KARACT U]	18 nF [GMC7.3182K250K3 1TR12]
18 nF [C0805C183K5HACT U]	18 nF [C1206C183K3GACT U]	18 nF [C1812C183K1GACT U]	18 nF [GMC7.3182K63K31 TR12]
18 nF [C0805C183K5RACT U]	18 nF [C1206C183K3HACT U]	18 nF [C1812C183K1HACT U]	18 nF [GMC7.3183K63K31 TR12]
18 nF [C0805C183K8RACT U]	18 nF [C1206C183K5HACT U]	18 nF [C1812C183K5GACT U]	18 nF [MMC5.7183K250J 35TR12]
18 nF [C0805C183KARACT U]	18 nF [C1206C183K5RACT U]	18 nF [C1812C183K5HACT U]	18 nF [MMC7.3183K250K 33TR12]
18 nF [C0805F183K1RACT U]	18 nF [C1210C183K1GACT U]	18 nF [C2220C183K2GACT U]	18 Ohm [4116R-1- 180]
18 nF [C0805F183K3RACT U]	18 nF [C1210C183K1HACT U]	18 nF [CA064C183K3RAC]	18 Ohm [4608X- 102-180LF]
18 nF [C0805F183K4RACT U]	18 nF [C1210C183K3HACT U]	18 nF [CDR03BX183BKSM]	18 Ohm [4816P-1- 180]
18 nF [C0805F183K5RACT U]	18 nF [C1210C183K5GACT U]	18 nF [GMC5.7182K250J3 1TR12]	18 Ohm [4816P- T01-180]
18 nF [C1206C183K1HACT U]	18 nF [C1210C183K5HACT U]	18 nF [GMC5.7183K100J3 1TR12]	18 Ohm [CAT10- 180J4LF]
18 nF [C1206C183K1RACT U]	18 nF [C1210C183K5RACT U]	18 nF [GMC5.7183K50J31 TR12]	18 Ohm [CAT16- 180J4LF]
			18 Ohm [CAT16- 180J8LF]

Multisim 14.1 Education Components

18 Ohm [CAT25-180JALF]	18 Ohm [CR1206-JW-180ELF]	18 pF [C0603C180K3GACTU]	18 pF [C1210C180KBGAC TU]
18 Ohm [CAY10-180J2LF]	18 Ohm [CR1206-JW-180GLF]	18 pF [C0603C180K5GACTU]	18 pF [C1812C180KBGAC TU]
18 Ohm [CAY10-180J4LF]	18 Ohm [CR2010-JW-180ELF]	18 pF [C0603C180K8GACTU]	18 pF [C1825C180KBGAC TU]
18 Ohm [CAY16-180J2LF]	18 Ohm [CR2512-JW-180ELF]	18 pF [C0805C180K1GACTU]	18 pF [C2220C180KBGAC TU]
18 Ohm [CAY16-180J4LF]	18 Ohm [CRM1206-FX-18R0ELF]	18 pF [C0805C180K2GACTU]	18 uF [C1210C186K4PACTU]
18 Ohm [CAY16-180J8LF]	18 Ohm [CRT0805-BW-18R0ELF]	18 pF [C0805C180K3GACTU]	18 uF [C1210C186K8PACTU]
18 Ohm [CR0201-JW-180GLF]	18 Ohm [CRT1206-CW-18R0ELF]	18 pF [C0805C180KBGAC TU]	18 uF [C1210C186K9PACTU]
18 Ohm [CR0402-FX-18R0GLF]	18 Ohm [FW20A18R0JA]	18 pF [C1206C180K1GACTU]	18 uH [SDE0403A-180M]
18 Ohm [CR0402-JW-180GLF]	18 pF [C0201C180K3GACTU]	18 pF [C1206C180K5GACTU]	18 uH [SDE0604A-180M]
18 Ohm [CR0603-FX-18R0ELF]	18 pF [C0402C180K3GACTU]	18 pF [C1206C180KBGAC TU]	18 uH [SDE0805A-180M]
18 Ohm [CR0603-JW-180ELF]	18 pF [C0402C180K5GACTU]	18 pF [C1206C180K1GACTU]	
18 Ohm [CR0603-JW-180GLF]	18 pF [C0402C180K8GACTU]	18 pF [C1206C180KBGAC TU]	
18 Ohm [CR0805-FX-18R0ELF]	18 pF [C0603C180K2GACTU]		
18 Ohm [CR0805-JW-180ELF]			
18 Ohm [CR1206-FX-18R0ELF]			

Multisim 14.1 Education Components

18 uH [SDE1006A-180M]	18 uH [SRR0735A-180M]	18 uH [SRR1260-180M]	18.2 kOhm [CR0805-FX-1822ELF]
18 uH [SDR0302-180ML]	18 uH [SRR0745A-180M]	18 uH [SRR1260A-180M]	18.2 kOhm [CR1206-FX-1822ELF]
18 uH [SDR0403-180ML]	18 uH [SRR0804-180Y]	18 uH [SRR1280-180M]	18.2 kOhm [CRT0603-BY-1822ELF]
18 uH [SDR0503-180ML]	18 uH [SRR0805-180Y]	18 uH [SRR4018-180Y]	18.2 kOhm [CRT0805-BY-1822ELF]
18 uH [SDR0603-180ML]	18 uH [SRR0905-180M]	18 uH [SRR4028-180Y]	18.2 kOhm [CRT0805-BY-1822ELF]
18 uH [SDR0604-180YL]	18 uH [SRR0906-180ML]	18 uH [SRR5018-180Y]	18.2 kOhm [CRT0805-PW-1822ELF]
18 uH [SDR0703-180KL]	18 uH [SRR0908-180ML]	18 uH [SRR5028-180Y]	18.2 Ohm [CR0402-FX-18R2GLF]
18 uH [SDR0805-180ML]	18 uH [SRR1003-180M]	18 uH [SRR6028-180Y]	18.2 Ohm [CR0603-FX-18R2ELF]
18 uH [SDR0906-180ML]	18 uH [SRR1005-180Y]	18 uH [SRR6038-180Y]	18.2 Ohm [CR0603-FX-18R2GLF]
18 uH [SDR1006-180ML]	18 uH [SRR1205-180ML]	18 uH [SRR6040A-180M]	18.2 Ohm [CR0805-FX-18R2ELF]
18 uH [SDR1105-180ML]	18 uH [SRR1206-180ML]	18 uH [SRR7045-180M]	18.2 Ohm [CR1206-FX-18R2ELF]
18 uH [SDR1307-180ML]	18 uH [SRR1208-180ML]	18 uH [SRU8043-180Y]	18.7 kOhm [CR0402-FX-1872GLF]
18 uH [SDR1307A-180M]	18 uH [SRR1210-180M]	18.2 kOhm [CR0603-FX-1822ELF]	18.7 kOhm [CR0603-FX-1872ELF]
18 uH [SRN1060-180M]	18 uH [SRR1210A-180M]		
18 uH [SRN3015-180M]	18 uH [SRR1240-180M]		

Multisim 14.1 Education Components

18.7 kOhm [CR0805-FX- 1872ELF]	180 kOhm [4308R- 101-184LF]	180 kOhm [4610X- 101-184LF]	180 kOhm [CR0402-FX- 1803GLF]
18.7 kOhm [CR1206-FX- 1872ELF]	180 kOhm [4308R- 102-184]	180 kOhm [4610X- 102-184LF]	180 kOhm [CR0402-JW- 184GLF]
18.7 Ohm [CR0603- FX-18R7ELF]	180 kOhm [4308R- 102-184LF]	180 kOhm [4816P- 1-184]	180 kOhm [CR0603-FX- 1803ELF]
18.7 Ohm [CR1206- FX-18R7ELF]	180 kOhm [4310M- 101-184]	180 kOhm [4816P- 1-184LF]	180 kOhm [CR0603-JW- 184ELF]
18.7 Ohm [CR2512- FX-18R7ELF]	180 kOhm [4310R- 101-184]	180 kOhm [4816P- 2-184]	180 kOhm [CR0603-JW- 184ELF]
180 kOhm [4114R- 1-184]	180 kOhm [4310R- 101-184LF]	180 kOhm [4816P- 2-184LF]	180 kOhm [CR0805-FX- 1803ELF]
180 kOhm [4114R- 1-184LF]	180 kOhm [4310R- 102-184]	180 kOhm [4816P- T01-184]	180 kOhm [CR0805-JW- 184ELF]
180 kOhm [4116R- 1-184]	180 kOhm [4416P- 1-184]	180 kOhm [4816P- T01-184LF]	180 kOhm [CR1206-FX- 1803ELF]
180 kOhm [4116R- 1-184LF]	180 kOhm [4605X- 101-184LF]	180 kOhm [4816P- T02-184]	180 kOhm [CR1206-JW- 184ELF]
180 kOhm [4116R- 2-184LF]	180 kOhm [4606X- 101-184LF]	180 kOhm [4816P- T02-184LF]	180 kOhm [CR2010-JW- 184ELF]
180 kOhm [4306R- 101-184]	180 kOhm [4606X- 102-184LF]	180 kOhm [CAT16- 184J4LF]	180 kOhm [CRM1206-JW- 184ELF]
180 kOhm [4306R- 101-184LF]	180 kOhm [4608X- 101-184LF]	180 kOhm [CAT25- 184JALF]	180 kOhm [CRM2512-JW- 184ELF]
180 kOhm [4306R- 102-184]	180 kOhm [4608X- 102-184LF]	180 kOhm [CAY16- 1803F4LF]	
180 kOhm [4306R- 102-184LF]	180 kOhm [4609X- 101-184LF]	180 kOhm [CAY16- 184J4LF]	
180 kOhm [4308R- 101-184]	180 kOhm [4610H- 102-184LF]	180 kOhm [CAY16- 184J8LF]	

Multisim 14.1 Education Components

180 kOhm [CRT1206-DY-1803ELF]	180 nF [C0805C184K3RACTU]	180 nF [C1210C184K1RACTU]	180 nF [C1812F184K2RACTU]
180 mOhm [CRL0603-FW-R180ELF]	180 nF [C0805C184K4RACTU]	180 nF [C1210C184K3HACTU]	180 nF [C1812F184K3RACTU]
180 mOhm [CRL0603-JW-R180ELF]	180 nF [C0805C184K5RACTU]	180 nF [C1210C184K5RACTU]	180 nF [C1812F184K5RACTU]
180 mOhm [CRL0805-FW-R180ELF]	180 nF [C0805C184K8RACTU]	180 nF [C1210F184K1RACTU]	180 nF [C1825C184K5RACTU]
180 mOhm [CRL0805-JW-R180ELF]	180 nF [C1206C184K1RACTU]	180 nF [C1210F184K3RACTU]	180 nF [C2225C184K1RACTU]
180 mOhm [CRL1206-FW-R180ELF]	180 nF [C1206C184K5RACTU]	180 nF [C1210F184K4RACTU]	180 nF [GMC5.7184K50J35TR12]
180 mOhm [CRL1206-JW-R180ELF]	180 nF [C1206C184M5UAC TU]	180 nF [C1210F184K5RACTU]	180 nF [GMC7.3184K63K33TR12]
180 mOhm [CRL2010-FW-R180ELF]	180 nF [C1206F184K1RACTU]	180 nF [C1812C184K1RACTU]	180 nF [MDC10184K100A52P3TUBE]
180 mOhm [CRL2010-JW-R180ELF]	180 nF [C1206F184K3RACTU]	180 nF [C1812C184K5HACTU]	180 nF [MDC10184K250A52P3TUBE]
180 nF [C0603C184K4RACTU]	180 nF [C1206F184K4RACTU]	180 nF [C1812C184K5RACTU]	180 nF [MDC10184K400A52P3TUBE]
180 nF [C0603C184K8RACTU]	180 nF [C1206F184K5RACTU]	180 nF [C1812F184K1RACTU]	180 nF [MDC10184K50A52P3TUBE]

Multisim 14.1 Education Components

180 nF [MDC10184K630A5 8P7TUBE]	180 Ohm [4114R-2- 181]	180 Ohm [4308R- 101-181]	180 Ohm [4420P- T01-181]
180 nF [MDC10184K630A5 8P8TUBE]	180 Ohm [4114R-2- 181LF]	180 Ohm [4308R- 101-181LF]	180 Ohm [4604X- 102-181LF]
180 nF [MDC15184K100B5 3P3TUBE]	180 Ohm [4116R-1- 181]	180 Ohm [4308R- 102-181]	180 Ohm [4605X- 101-181LF]
180 nF [MDC15184K250B5 3P3TUBE]	180 Ohm [4116R-2- 181]	180 Ohm [4308R- 102-181LF]	180 Ohm [4606X- 101-181LF]
180 nF [MDC15184K250B5 3P3TUBE]	180 Ohm [4116R-2- 181LF]	180 Ohm [4309R- 101-181]	180 Ohm [4606X- 102-181LF]
180 nF [MDC15184K400B5 3P3TUBE]	180 Ohm [4116R-2- 181LF]	180 Ohm [4310M- 101-181]	180 Ohm [4607X- 101-181LF]
180 nF [MDC15184K50B53 P3TUBE]	180 Ohm [4306H- 101-181]	180 Ohm [4310M- 101-181LF]	180 Ohm [4608X- 101-181LF]
180 nF [MDC15184K50B53 P3TUBE]	180 Ohm [4306H- 101-181LF]	180 Ohm [4310R- 101-181]	180 Ohm [4608X- 102-181LF]
180 nF [MDK15184K50B53 P3TUBE]	180 Ohm [4306R- 101-181]	180 Ohm [4310R- 101-181LF]	180 Ohm [4608X- AP1-181LF]
180 nF [MDS15184K400B5 3P3TUBE]	180 Ohm [4306R- 101-181LF]	180 Ohm [4310R- 102-181]	180 Ohm [4609X- 101-181LF]
180 nF [MDS15184K400B5 3P3TUBE]	180 Ohm [4306R- 102-181]	180 Ohm [4310R- 102-181LF]	180 Ohm [4610H- 101-181LF]
180 nF [MDS15184K50B53 P3TUBE]	180 Ohm [4306R- 102-181LF]	180 Ohm [4416P-1- 181]	180 Ohm [4610M- 101-181LF]
180 nF [MMC7.3184K50K3 3TR12]	180 Ohm [4308H- 101-181]	180 Ohm [4416P-2- 181]	180 Ohm [4610X- 101-181LF]
180 Ohm [4114R-1- 181]	180 Ohm [4308M- 101-181]	180 Ohm [4416P- T01-181]	180 Ohm [4610X- 102-181LF]
180 Ohm [4114R-1- 181LF]	180 Ohm [4308M- 101-181LF]	180 Ohm [4420P-1- 181]	180 Ohm [4610X- AP1-181LF]

Multisim 14.1 Education Components

180 Ohm [4612X-102-181LF]	180 Ohm [4820P-1-181]	180 Ohm [CR0805-FX-1800GLF]	180 Ohm [PWR6327W1800JE]
180 Ohm [4814P-1-181]	180 Ohm [CAT10-181J4LF]	180 Ohm [CR0805-JW-181ELF]	180 pF [C0402C181K1HACTU]
180 Ohm [4814P-2-181]	180 Ohm [CAT16-1800F4LF]	180 Ohm [CR0805-JW-181GLF]	180 pF [C0402C181K3HACTU]
180 Ohm [4814P-2-181LF]	180 Ohm [CAT16-181J4LF]	180 Ohm [CR1206-FX-1800ELF]	180 pF [C0402C181K3RACTU]
180 Ohm [4814P-T01-181]	180 Ohm [CAT16-181J8LF]	180 Ohm [CR1206-JW-181ELF]	180 pF [C0402C181K3RACTU]
180 Ohm [4814P-T01-181LF]	180 Ohm [CAT25-181JALF]	180 Ohm [CR2010-JW-181ELF]	180 pF [C0402C181K4RACTU]
180 Ohm [4814P-T02-181]	180 Ohm [CAY10-181J4LF]	180 Ohm [CR2512-FX-1800ELF]	180 pF [C0402C181K5HACTU]
180 Ohm [4816P-1-181]	180 Ohm [CAY16-181J4LF]	180 Ohm [CR2512-JW-181ELF]	180 pF [C0402C181K5RACTU]
180 Ohm [4816P-1-181LF]	180 Ohm [CAY16-181J8LF]	180 Ohm [CRT0805-FV-1800ELF]	180 pF [C0402C181K5RACTU]
180 Ohm [4816P-2-181]	180 Ohm [CR0402-FX-1800GLF]	180 Ohm [PWR2010W1800JE]	180 pF [C0402C181K8RACTU]
180 Ohm [4816P-2-181LF]	180 Ohm [CR0402-JW-181GLF]	180 Ohm [PWR263S-35-1800J]	180 pF [C0603C181K1RACTU]
180 Ohm [4816P-T01-181]	180 Ohm [CR0603-FX-1800ELF]	180 Ohm [PWR4525W1800J]	180 pF [C0603C181K2RACTU]
180 Ohm [4816P-T01-181LF]	180 Ohm [CR0603-JW-181ELF]	180 Ohm [PWR5322W1800JE]	180 pF [C0603C181K3RACTU]
180 Ohm [4816P-T02-181]	180 Ohm [CR0603-JW-181GLF]		
180 Ohm [4816P-T02-181LF]	180 Ohm [CR0805-FX-1800ELF]		

Multisim 14.1 Education Components

180 pF [C0603C181K4RACT U]	180 pF [C1210C181KBGAC TU]	180 uF [A700D187M002AT E015]	180 uF [EEFCX0J181R]
180 pF [C0603C181K5GACT U]	180 pF [C1812C181KBGAC TU]	180 uF [A700D187M002AT E018]	180 uF [EEFLR0E181R]
180 pF [C0603C181K5RACT U]	180 pF [C1825C181KBGAC TU]	180 uF [A700D187M004AT E015]	180 uF [EEFLR0E181R4]
180 pF [C0603C181K8RACT U]	180 pF [C2220C181KBGAC TU]	180 uF [A700D187M004AT E018]	180 uF [EEFSR0E181R]
180 pF [C0805C181K1GACT U]	180 pF [C2225C181KBGAC TU]	180 uF [A700D187M2R5AT E015]	180 uF [EEFSR0E181R4]
180 pF [C0805C181K2GACT U]	180 pF [CA064C181K4GAC TU]	180 uF [A700D187M2R5AT E018]	180 uF [EEFSR0E181R]
180 pF [C0805C181K5GACT U]	180 pF [CA064C181K5GAC TU]	180 uF [A700X187M004AT E010]	180 uF [EEFSX0E181ER]
180 pF [C1206C181K1GACT U]	180 uF [16SEPF180M]	180 uF [A700X187M006AT E010]	180 uF [EEFSX0G181ER]
180 pF [C1206C181K2GACT U]	180 uF [16SVPE180M]	180 uF [A700X187M006AT E015]	180 uH [SDE0805A- 181K]
180 pF [C1206C181K5GACT U]	180 uF [2R5SVPC180MY]	180 uF [EEFCT0G181R]	180 uH [SDE1006A- 181K]
180 pF [C1206C181KBGAC TU]	180 uF [6SVPE180M]	180 uF [EEFCX0G181R]	180 uH [SDR0302- 181KL]
		180 uF [EEFCX0G181XR]	180 uH [SDR0403- 181KL]

Multisim 14.1 Education Components

180 uH [SDR0503-181KL]	180 uH [SRR0908-181YL]	180 uH [SRR7045-181M]	182 Ohm [CR0805-FX-1820ELF]
180 uH [SDR0603-181KL]	180 uH [SRR1003-181M]	181-015-113R431	182 Ohm [CR1206-FX-1820ELF]
180 uH [SDR0604-181KL]	180 uH [SRR1005-181K]	181-015-213R431	182 Ohm [CRT0402-DZ-1820GLF]
180 uH [SDR0703-181KL]	180 uH [SRR1205-181KL]	181-026-113R431	182 Ohm [CRT0603-BY-1820ELF]
180 uH [SDR0805-181KL]	180 uH [SRR1206-181KL]	181-044-113R431	182-009-113R431
180 uH [SDR0906-181KL]	180 uH [SRR1208-181YL]	181-044-213R431	182-009-213R431
180 uH [SDR1006-181KL]	180 uH [SRR1210-181M]	181-062-113R431	182-015-113R431
180 uH [SDR1307-181KL]	180 uH [SRR1210A-181M]	181-062-213R431	182-015-213R431
180 uH [SDR1307A-181K]	180 uH [SRR1240-181K]	181-078-113R431	182-025-113R431
180 uH [SRR0735A-181M]	180 uH [SRR1260-181K]	181-078-213R431	182-025-213R431
180 uH [SRR0745A-181M]	180 uH [SRR1260A-181K]	182 kOhm [CR0402-FX-1823GLF]	182-037-113R431
180 uH [SRR0804-181K]	180 uH [SRR1280-181K]	182 kOhm [CR0603-FX-1823ELF]	182-037-213R431
180 uH [SRR0805-181K]	180 uH [SRR4018-181Y]	182 kOhm [CR0805-FX-1823ELF]	183-009-113R161
180 uH [SRR0905-181K]	180 uH [SRR4028-181Y]	182 kOhm [CR1206-FX-1823ELF]	183-009-213R161
180 uH [SRR0906-181YL]	180 uH [SRR5018-181Y]	182 Ohm [CAY16-1820F4LF]	183-015-113R161
		182 Ohm [CR0402-FX-1820GLF]	183-015-213R161
		182 Ohm [CR0603-FX-1820ELF]	183-025-113R161
			183-025-213R161
			183-037-113R161
			183-037-213R161

Multisim 14.1 Education Components

187 kOhm [CR0402-FX- 1873GLF]	19 kOhm [PWR263S-35- 1902JE]	19.6 kOhm [CR0805-FX- 1962ELF]	191 kOhm [CRT0805-BY- 1913ELF]
187 kOhm [CR0603-FX- 1873ELF]	19.1 kOhm [CAT16- 1912F4LF]	19.6 kOhm [CR1206-FX- 1962ELF]	191 Ohm [CR0201- FW-1910GLF]
187 kOhm [CR0603-FX- 1873GLF]	19.1 kOhm [CR0201-FW- 1912GLF]	19.6 kOhm [CRT0402-FZ- 1962GLF]	191 Ohm [CR0402- FX-1910GLF]
187 kOhm [CR0805-FX- 1873ELF]	19.1 kOhm [CR0402-FX- 1912GLF]	19.6 kOhm [CRT0805-BY- 1962ELF]	191 Ohm [CR0603- FX-1910ELF]
187 kOhm [CR1206-FX- 1873ELF]	19.1 kOhm [CR0603-FX- 1912ELF]	19.6 Ohm [CR0805- FX-19R6ELF]	191 Ohm [CR1206- FX-1910ELF]
187 kOhm [CRT0805-BY- 1873ELF]	19.1 kOhm [CR0805-FX- 1912ELF]	19.6 Ohm [CR1206- FX-19R6ELF]	1932258-1
187 Ohm [CR0402- FX-1870GLF]	19.1 kOhm [CR1206-FX- 1912ELF]	19.6 Ohm [CRT0402-FZ- 19R6GLF]	196 kOhm [CR0603-FX- 1963ELF]
187 Ohm [CR0603- FX-1870ELF]	19.1 kOhm [CRT0603-BY- 1912ELF]	191 kOhm [CR0402-FX- 1913GLF]	196 kOhm [CR0805-FX- 1963ELF]
187 Ohm [CR0805- FX-1870ELF]	19.1 Ohm [CR0805- FX-19R1ELF]	191 kOhm [CR0603-FX- 1913ELF]	196 kOhm [CR1206-FX- 1963ELF]
187 Ohm [CR1206- FX-1870ELF]	19.1 Ohm [CR1206- FX-19R1ELF]	191 kOhm [CR0805-FX- 1913ELF]	196 Ohm [CR0603- FX-1960ELF]
187 Ohm [CRT1206-FZ- 1870ELF]	19.6 kOhm [CR0402-FX- 1962GLF]	191 kOhm [CR1206-FX- 1913ELF]	196 Ohm [CR0805- FX-1960ELF]
18TQ045	19.6 kOhm [CR0603-FX- 1962ELF]	191 kOhm [CRT0402-BY- 1913GLF]	196 Ohm [CRT0402-FZ- 1960GLF]

Multisim 14.1 Education Components

1981584-1	1N3613GP	1N3890A	1N4003GP
1B4B42	1N3614GP	1N3891	1N4003RLG
1BH62	1N3659	1N3891A	1N4004G
1DH62	1N3660	1N3892	1N4004GP
1G4B42	1N3661	1N3892A	1N4004RLG
1GH62	1N3662	1N3893	1N4005G
1J4B42	1N3663	1N3893A	1N4005GP
1JH62	1N3712	1N3899	1N4005RLG
1L2.5SP	1N3713	1N3900	1N4006FFG
1L5SP	1N3714	1N3901	1N4006G
1LH62	1N3715	1N3902	1N4006GP
1N1199C	1N3720	1N3903	1N4006RLG
1N1200C	1N3879	1N3909	1N4007-E3/54
1N1202C	1N3879A	1N3910	1N4007FFG
1N1204C	1N3880	1N3911	1N4007G
1N1206C	1N3880A	1N3912	1N4007GP
1N3064	1N3881	1N3913	1N4007RLG
1N3208	1N3881A	1N3957GP	1N4009
1N3491	1N3882	1N4001G	1N4148
1N3492	1N3882A	1N4001GP	1N4149
1N3493	1N3883	1N4001RLG	1N4150
1N3494	1N3883A	1N4002G	1N4151
1N3495	1N3889	1N4002GP	1N4152
1N3611GP	1N3889A	1N4002RLG	1N4153
1N3612GP	1N3890	1N4003G	1N4154

Multisim 14.1 Education Components

1N4245GP	1N4732A	1N4757A	1N4944GP
1N4246GP	1N4733A	1N4758A	1N4946GP
1N4247GP	1N4734A	1N4759A	1N4947GP
1N4248GP	1N4735A	1N4760A	1N4948GP
1N4249GP	1N4736A	1N4761A	1N5059GP
1N4305	1N4737A	1N4762A	1N5060GP
1N4370A	1N4738A	1N4763A	1N5061GP
1N4371A	1N4739A	1N4764A	1N5062GP
1N4372A	1N4740A	1N4933	1N5221B
1N4383GP	1N4741A	1N4933G	1N5222B
1N4384GP	1N4742A	1N4933RLG	1N5223B
1N4385GP	1N4743A	1N4934	1N5224B
1N4446	1N4744A	1N4934G	1N5225B
1N4447	1N4745A	1N4934RLG	1N5226B
1N4448	1N4746A	1N4935	1N5227B
1N4449	1N4747A	1N4935G	1N5228B
1N4454	1N4748A	1N4935RLG	1N5229B
1N4585GP	1N4749A	1N4936	1N5230B
1N4586GP	1N4750A	1N4936G	1N5231B
1N4678	1N4751A	1N4936RLG	1N5232B
1N4681	1N4752A	1N4937	1N5233B
1N4728A	1N4753A	1N4937G	1N5234B
1N4729A	1N4754A	1N4937RLG	1N5235B
1N4730A	1N4755A	1N4938	1N5236B
1N4731A	1N4756A	1N4942GP	1N5237B

Multisim 14.1 Education Components

1N5238B	1N5263B	1N5337BG	1N5350BG
1N5239B	1N5264B	1N5337BRLG	1N5350BRLG
1N5240B	1N5265B	1N5338BG	1N5351BG
1N5241B	1N5266B	1N5338BRLG	1N5351BRLG
1N5242B	1N5267B	1N5339BG	1N5352BG
1N5243B	1N5268B	1N5339BRLG	1N5352BRLG
1N5244B	1N5269B	1N5340BG	1N5353BG
1N5245B	1N5270B	1N5340BRLG	1N5353BRLG
1N5246B	1N5271B	1N5341BG	1N5355BG
1N5247B	1N5272B	1N5341BRLG	1N5355BRLG
1N5248B	1N5273B	1N5342BG	1N5356BRLG
1N5249B	1N5274B	1N5342BRLG	1N5357BG
1N5250B	1N5275B	1N5343BG	1N5357BRLG
1N5251B	1N5276B	1N5343BRLG	1N5358BG
1N5252B	1N5277B	1N5344BG	1N5358BRLG
1N5253B	1N5278B	1N5344BRLG	1N5359BG
1N5254B	1N5279B	1N5345BRLG	1N5359BRLG
1N5255B	1N5280B	1N5346BG	1N5361BG
1N5256B	1N5281B	1N5346BRLG	1N5361BRLG
1N5257B	1N5333BRLG	1N5347BG	1N5362BG
1N5258B	1N5334BRLG	1N5347BRLG	1N5362BRLG
1N5259B	1N5335BG	1N5348BG	1N5363BG
1N5260B	1N5335BRLG	1N5348BRLG	1N5363BRLG
1N5261B	1N5336BG	1N5349BG	1N5364BG
1N5262B	1N5336BRLG	1N5349BRLG	1N5364BRLG

Multisim 14.1 Education Components

1N5365BG	1N5384BRLG	1N5404G	1N5818G
1N5365BRLG	1N5386BG	1N5404RLG	1N5818RLG
1N5366BG	1N5386BRLG	1N5406	1N5819G
1N5366BRLG	1N5388BG	1N5406G	1N5819RLG
1N5367BG	1N5388BRLG	1N5406RLG	1N5820
1N5367BRLG	1N5391	1N5407G	1N5820G
1N5368BG	1N5391GP	1N5407RLG	1N5820RLG
1N5368BRLG	1N5392GP	1N5408-E3/54	1N5821
1N5369BG	1N5393GP	1N5408G	1N5821G
1N5369BRLG	1N5394GP	1N5408RLG	1N5821RLG
1N5371BRLG	1N5395GP	1N5615GP	1N5822
1N5372BG	1N5396GP	1N5617GP	1N5822-E3/54
1N5372BRLG	1N5397GP	1N5619GP	1N5822G
1N5373BG	1N5398GP	1N5621GP	1N5822RLG
1N5373BRLG	1N5399GP	1N5623GP	1N5823
1N5374BG	1N5400	1N5758	1N5824
1N5374BRLG	1N5400G	1N5758A	1N5825
1N5375BG	1N5400RLG	1N5759	1N5826
1N5375BRLG	1N5401	1N5759A	1N5827
1N5378BG	1N5401G	1N5760	1N5828
1N5378BRLG	1N5401RLG	1N5761	1N5829
1N5381BRLG	1N5402	1N5761A	1N5830
1N5383BG	1N5402G	1N5817-E3/54	1N5831
1N5383BRLG	1N5402RLG	1N5817G	1N5832
1N5384BG	1N5404	1N5817RLG	1N5833

Multisim 14.1 Education Components

1N5834	1N5927BG	1N5941B	1N5994B
1N5913B	1N5927BRLG	1N5941BRLG	1N5995B
1N5913BRLG	1N5928B	1N5942B	1N5996B
1N5914B	1N5929B	1N5942BRLG	1N5997B
1N5915B	1N5929BG	1N5943B	1N5998B
1N5916B	1N5929BRLG	1N5944B	1N5999B
1N5917B	1N5930B	1N5945B	1N6000B
1N5918B	1N5931B	1N5946B	1N6001B
1N5919B	1N5931BRLG	1N5946BRLG	1N6002B
1N5919BG	1N5932B	1N5947B	1N6003B
1N5919BRLG	1N5932BRLG	1N5948BRLG	1N6004B
1N5920B	1N5933B	1N5953BG	1N6005B
1N5920BG	1N5934B	1N5953BRLG	1N6006B
1N5921B	1N5934BG	1N5955BRLG	1N6007B
1N5921BG	1N5934BRLG	1N5956BG	1N6008B
1N5921BRLG	1N5935B	1N5956BRLG	1N6009B
1N5922B	1N5935BRLG	1N5985B	1N6010B
1N5923B	1N5936B	1N5986B	1N6011B
1N5923BRLG	1N5937B	1N5987B	1N6012B
1N5924B	1N5937BRLG	1N5988B	1N6013B
1N5924BRLG	1N5938B	1N5989B	1N6014B
1N5925B	1N5938BRLG	1N5990B	1N6015B
1N5925BRLG	1N5939B	1N5991B	1N6016B
1N5926B	1N5940B	1N5992B	1N6017B
1N5927B	1N5940BRLG	1N5993B	1N6018B

Multisim 14.1 Education Components

1N6019B	1N748A	1N964B	1N989B
1N6020B	1N749A	1N965B	1N990B
1N6021B	1N750A	1N966B	1N991B
1N6022B	1N751A	1N967B	1N992B
1N6023B	1N752A	1N968B	1P1S
1N6024B	1N753A	1N969B	1P1S_TAPPED
1N6025B	1N754A	1N970B	1P2S
1N6096	1N755A	1N971B	1P3S
1N6098	1N756A	1N972B	1P4S
1N6285AG	1N757A	1N973B	1P5S
1N6285ARL4G	1N758A	1N974B	1PMT12AT1G
1N6287AG	1N759A	1N975B	1PMT16AT3G
1N6287ARL4G	1N914	1N976B	1PMT33AT3G
1N6292AG	1N914A	1N977B	1PMT5.0AT1G
1N6292ARL4G	1N914B	1N978B	1PMT5927BT1G
1N6294ARL4G	1N916	1N979B	1PS10SB82
1N6373-E3/51	1N916A	1N980B	1PS300
1N6478	1N916B	1N981B	1PS301
1N6479	1N957B	1N982B	1PS302
1N6480	1N958B	1N983B	1PS66SB17
1N6481	1N959B	1N984B	1PS66SB82
1N6482	1N960B	1N985B	1PS70SB10
1N6483	1N961B	1N986B	1PS70SB14
1N6484	1N962B	1N987B	1PS70SB15
1N747A	1N963B	1N988B	1PS70SB16

Multisim 14.1 Education Components

1PS70SB20	1S1555	1SMB14AT3G	1SMB5927BT3G
1PS70SB40	1S1830	1SMB170AT3G	1SMB5930BT3G
1PS70SB44	1S1834	1SMB18CAT3G	1SMB5931BT3G
1PS70SB45	1S1835	1SMB20CAT3G	1SMB5933BT3G
1PS70SB46	1S1885	1SMB22CAT3G	1SMB5934BT3G
1PS70SB82	1S1887	1SMB24AT3G	1SMB5935BT3G
1PS70SB84	1S1888	1SMB24CAT3G	1SMB5936BT3G
1PS70SB85	1S953	1SMB26CAT3G	1SMB5937BT3G
1PS70SB86	1S954	1SMB28AT3G	1SMB5939BT3G
1PS74SB23	1S955	1SMB28CAT3G	1SMB5940BT3G
1PS75SB45	1SMA12CAT3G	1SMB30AT3G	1SMB70AT3G
1PS76SB10	1SMA26AT3G	1SMB30CAT3G	1SMB85AT3G
1PS76SB17	1SMA30AT3G	1SMB33CAT3G	1SMC28AT3G
1PS76SB40	1SMA40CAT3G	1SMB36CAT3G	1SMC36AT3G
1PS76SB70	1SMA5.0AT3G	1SMB5.0AT3G	1SMC6.0AT3G
1PS79SB10	1SMA5913BT3G	1SMB54CAT3G	1SS400T1G
1PS79SB17	1SMA5918BT3G	1SMB58CAT3G	1SV233-TB-E
1PS79SB30	1SMA5921BT3G	1SMB5914BT3G	1SV234-TB-E
1PS79SB31	1SMA5922BT3G	1SMB5918BT3G	1Z10
1PS79SB40	1SMA5927BT3G	1SMB5919BT3G	1Z11
1PS79SB70	1SMA5931BT3G	1SMB5920BT3G	1Z12
1PS88SB48	1SMA5932BT3G	1SMB5921BT3G	1Z13
1PS88SB82	1SMA5936BT3G	1SMB5922BT3G	1Z14
1S1553	1SMA5940BT3G	1SMB5924BT3G	1Z15
1S1554	1SMB12AT3G	1SMB5925BT3G	1Z30

Multisim 14.1 Education Components

1Z6.2	2 kOhm [4116R-1-202]	2 kOhm [4308M-102-202LF]	2 kOhm [4310R-102-202LF]
1Z6.8			
1Z7.5	2 kOhm [4116R-1-202LF]	2 kOhm [4308R-101-202]	2 kOhm [4416P-1-202]
1Z8.2	2 kOhm [4116R-2-202]	2 kOhm [4308R-101-202LF]	2 kOhm [4416P-T01-202]
1Z9.1			
1ZB10	2 kOhm [4116R-2-202LF]	2 kOhm [4308R-102-202]	2 kOhm [4420P-2-202]
1ZB11	2 kOhm [4304M-101-202]	2 kOhm [4308R-102-202LF]	2 kOhm [4420P-2-202LF]
1ZB12			
1ZB13	2 kOhm [4304M-101-202LF]	2 kOhm [4309R-101-202]	2 kOhm [4420P-T02-202]
1ZB14			
1ZB15	2 kOhm [4306M-101-202]	2 kOhm [4309R-101-202LF]	2 kOhm [4604X-101-202LF]
1ZB30	2 kOhm [4306M-102-202]	2 kOhm [4310H-101-202]	2 kOhm [4604X-102-202LF]
1ZB6.8			
1ZB7.5	2 kOhm [4306M-102-202LF]	2 kOhm [4310H-101-202LF]	2 kOhm [4605X-101-202LF]
1ZB8.2	2 kOhm [4306R-101-202]	2 kOhm [4310M-101-202]	2 kOhm [4606X-101-202LF]
1ZB9.1			
2 kOhm [4108R-1-202LF]	2 kOhm [4306R-101-202LF]	2 kOhm [4310M-102-202]	2 kOhm [4606X-102-202LF]
2 kOhm [4114R-1-202]	2 kOhm [4306R-102-202]	2 kOhm [4310M-102-202LF]	2 kOhm [4606X-AP2-202LF]
2 kOhm [4114R-1-202LF]	2 kOhm [4306R-102-202LF]	2 kOhm [4310R-101-202]	2 kOhm [4608H-101-202LF]
2 kOhm [4114R-2-202]	2 kOhm [4308H-102-202]	2 kOhm [4310R-101-202LF]	2 kOhm [4608H-102-202LF]
2 kOhm [4114R-2-202LF]	2 kOhm [4308M-102-202]	2 kOhm [4310R-102-202]	2 kOhm [4608X-101-202LF]

Multisim 14.1 Education Components

2 kOhm [4608X-102-202LF]	2 kOhm [4814P-2-202]	2 kOhm [4818P-2-202LF]	2 kOhm [CAY16-202J4LF]
2 kOhm [4608X-AP1-202LF]	2 kOhm [4814P-2-202LF]	2 kOhm [4818P-T02-202]	2 kOhm [CAY17-202JALF]
2 kOhm [4608X-AP2-202LF]	2 kOhm [4814P-T01-202]	2 kOhm [4820P-2-202]	2 kOhm [CR0201-FW-2001GLF]
2 kOhm [4609M-101-202LF]	2 kOhm [4814P-T01-202LF]	2 kOhm [4820P-2-202F]	2 kOhm [CR0201-JW-202GLF]
2 kOhm [4609X-101-202LF]	2 kOhm [4814P-T02-202]	2 kOhm [4820P-T01-202]	2 kOhm [CR0402-FX-2001GLF]
2 kOhm [4610H-101-202LF]	2 kOhm [4814P-T02-202LF]	2 kOhm [4820P-T02-202]	2 kOhm [CR0402-JW-202GLF]
2 kOhm [4610H-102-202LF]	2 kOhm [4816P-1-202]	2 kOhm [CAT10-202J4LF]	2 kOhm [CR0603-FX-2001ELF]
2 kOhm [4610X-101-202LF]	2 kOhm [4816P-1-202LF]	2 kOhm [CAT16-2001F4LF]	2 kOhm [CR0603-JW-202ELF]
2 kOhm [4610X-102-202LF]	2 kOhm [4816P-2-202]	2 kOhm [CAT16-202J2LF]	2 kOhm [CR0603-JW-202GLF]
2 kOhm [4610X-AP1-202LF]	2 kOhm [4816P-2-202LF]	2 kOhm [CAT16-202J4LF]	2 kOhm [CR0805-FX-2001ELF]
2 kOhm [4611X-101-202LF]	2 kOhm [4816P-T01-202]	2 kOhm [CAT16-202J8LF]	2 kOhm [CR0805-JW-202ELF]
2 kOhm [4612X-101-202LF]	2 kOhm [4816P-T01-202LF]	2 kOhm [CAT25-202JALF]	2 kOhm [CR0805-JW-202GLF]
2 kOhm [4612X-102-202LF]	2 kOhm [4816P-T02-202]	2 kOhm [CAY10-202J4LF]	2 kOhm [CR1206-FX-2001ELF]
2 kOhm [4814P-1-202]	2 kOhm [4816P-T02-202LF]	2 kOhm [CAY16-2001F4LF]	2 kOhm [CR1206-FX-2001GLF]
2 kOhm [4814P-1-202LF]	2 kOhm [4818P-2-202]	2 kOhm [CAY16-202J2LF]	2 kOhm [CR1206-JW-202ELF]

Multisim 14.1 Education Components

2 kOhm [CR1206-JW-202GLF]	2 kOhm [PWR221T-30-2001F]	2 mOhm [CRE2512-FZ-R002E-3]	2 nF [C2225C202KBGAC TU]
2 kOhm [CR2010-JW-202ELF]	2 kOhm [PWR263S-35-2001J]	2 mOhm [CRF2512-FX-R002ELF]	2 Ohm [CR0402-J/-2R0GLF]
2 kOhm [CR2512-FX-2001ELF]	2 kOhm [PWR4525W2001J]	2 mOhm [CRF2512-JV-R002ELF]	2 Ohm [CR0402-JW-2R0GLF]
2 kOhm [CRM1206-FX-2001ELF]	2 kOhm [PWR4525W2001JE]	2 MOhm [CRT1206-DZ-2004ELF]	2 Ohm [CR0603-J/-2R0ELF]
2 kOhm [CRM2512-JW-202ELF]	2 MOhm [4116R-1-205LF]	2 mOhm [CST0612-FC-R002E]	2 Ohm [CR0805-J/-2R0ELF]
2 kOhm [CRT0402-FZ-2001GLF]	2 MOhm [4608X-102-205LF]	2 nF [C0603C202K1HACT U]	2 Ohm [CR1206-J/-2R0ELF]
2 kOhm [CRT0603-BY-2001ELF]	2 MOhm [4610X-101-205LF]	2 nF [C0603C202K3HACT U]	2 Ohm [CRL0603-FW-2R00ELF]
2 kOhm [CRT0603-DY-2001ELF]	2 MOhm [4816P-1-205]	2 nF [C0603C202K5HACT U]	2 Ohm [CRL0603-JW-2R00ELF]
2 kOhm [CRT0603-FY-2001ELF]	2 MOhm [4816P-1-205LF]	2 nF [C1210C202KCGAC TU]	2 Ohm [CRL0805-FW-2R00ELF]
2 kOhm [CRT0603-PV-2001ELF]	2 MOhm [CR0603-FW-2004ELF]	2 nF [C1812C202KBGAC TU]	2 Ohm [CRL0805-JW-2R00ELF]
2 kOhm [CRT0603-PW-2001ELF]	2 MOhm [CR0603-JW-205ELF]	2 nF [C1825C202KBGAC TU]	2 Ohm [CRL1206-FW-2R00ELF]
2 kOhm [CRT0805-BY-2001ELF]	2 MOhm [CR0805-JW-205ELF]	2 nF [C2220C202KBGAC TU]	2 Ohm [CRM1206-FX-2R00ELF]
2 kOhm [CRT1206-BY-2001ELF]	2 MOhm [CR1206-FW-2004ELF]		
2 kOhm [PWR220T-35-2001J]	2 MOhm [CR1206-JW-205ELF]		
	2 mOhm [CRE2512-FZ-R002E-2]		

Multisim 14.1 Education Components

2 Ohm [CRM2010-JW-2R0ELF]	2 Ohm [PWR263S-20-2R00J]	2.05 kOhm [CR0603-FX-2051ELF]	2.15 kOhm [CRT0402-FZ-2151GLF]
2 Ohm [CRM2512-FX-2R00ELF]	2 Ohm [PWR263S-20-2R00JE]	2.05 kOhm [CR0805-FX-2051ELF]	2.2 kOhm [4108R-1-222]
2 Ohm [CRM2512-JW-2R0ELF]	2 Ohm [PWR263S-35-2R00F]	2.05 kOhm [CR1206-FX-2051ELF]	2.2 kOhm [4108R-1-222LF]
2 Ohm [CRT0805-CY-2R00ELF]	2 Ohm [PWR263S-35-2R00J]	2.05 kOhm [CRT0402-FZ-2051GLF]	2.2 kOhm [4114R-1-222]
2 Ohm [PWR163S-25-2R00F]	2 Ohm [PWR3014W2R00JE]	2.05 kOhm [CR0402-FX-2101GLF]	2.2 kOhm [4114R-2-222]
2 Ohm [PWR163S-25-2R00FE]	2 Ohm [PWR4318W2R00JE]	2.1 kOhm [CR0603-FX-2101ELF]	2.2 kOhm [4114R-2-222LF]
2 Ohm [PWR163S-25-2R00J]	2 Ohm [PWR5322W2R00JE]	2.1 kOhm [CR0805-FX-2101ELF]	2.2 kOhm [4116R-1-222]
2 Ohm [PWR163S-25-2R00JE]	2 Ohm [PWR6327N2R00F]	2.1 kOhm [CR1206-FX-2101ELF]	2.2 kOhm [4116R-2-222]
2 Ohm [PWR220T-20-2R00F]	2 uH [SRP1204-1R8M]	2.15 kOhm [CR0402-FX-2151GLF]	2.2 kOhm [4116R-2-222LF]
2 Ohm [PWR220T-20-2R00J]	2 uH [SRP1205-1R8Y]	2.15 kOhm [CR0603-FX-2151ELF]	2.2 kOhm [4304M-101-222]
2 Ohm [PWR220T-35-2R00F]	2 uH [SRR1305-2R0ZL]	2.15 kOhm [CR0805-FX-2151ELF]	2.2 kOhm [4304M-102-222]
2 Ohm [PWR221T-30-2R00F]	2 uH [SRU3014-2R0Y]	2.15 kOhm [CR1206-FX-2151ELF]	2.2 kOhm [4304M-102-222LF]
2 Ohm [PWR2615W2R00J]	2.05 kOhm [CR0402-FX-2051GLF]		
2 Ohm [PWR263S-20-2R00F]			
2 Ohm [PWR263S-20-2R00FE]			

Multisim 14.1 Education Components

2.2 kOhm [4306H-101-222]	2.2 kOhm [4308M-102-222LF]	2.2 kOhm [4310R-101-222LF]	2.2 kOhm [4605X-101-222LF]
2.2 kOhm [4306H-101-222LF]	2.2 kOhm [4308R-101-222]	2.2 kOhm [4310R-102-222]	2.2 kOhm [4605X-AP1-222LF]
2.2 kOhm [4306M-101-222]	2.2 kOhm [4308R-101-222LF]	2.2 kOhm [4310R-102-222LF]	2.2 kOhm [4606H-101-222LF]
2.2 kOhm [4306M-102-222]	2.2 kOhm [4308R-102-222]	2.2 kOhm [4311R-101-222]	2.2 kOhm [4606M-101-222LF]
2.2 kOhm [4306M-102-222LF]	2.2 kOhm [4308R-102-222LF]	2.2 kOhm [4311R-101-222LF]	2.2 kOhm [4606M-102-222LF]
2.2 kOhm [4306R-101-222]	2.2 kOhm [4309R-101-222]	2.2 kOhm [4416P-1-222]	2.2 kOhm [4606X-101-222LF]
2.2 kOhm [4306R-101-222LF]	2.2 kOhm [4309R-101-222LF]	2.2 kOhm [4416P-2-222]	2.2 kOhm [4606X-102-222LF]
2.2 kOhm [4306R-102-222]	2.2 kOhm [4310H-101-222]	2.2 kOhm [4416P-T01-222]	2.2 kOhm [4606X-AP1-222LF]
2.2 kOhm [4306R-102-222LF]	2.2 kOhm [4310H-101-222LF]	2.2 kOhm [4416P-T02-222]	2.2 kOhm [4606X-AP2-222LF]
2.2 kOhm [4308H-101-222]	2.2 kOhm [4310H-102-222]	2.2 kOhm [4420P-2-222]	2.2 kOhm [4607M-101-222LF]
2.2 kOhm [4308H-102-222]	2.2 kOhm [4310M-101-222]	2.2 kOhm [4420P-T01-222]	2.2 kOhm [4607X-101-222LF]
2.2 kOhm [4308H-102-222LF]	2.2 kOhm [4310M-101-222LF]	2.2 kOhm [4420P-T02-222]	2.2 kOhm [4608H-102-222LF]
2.2 kOhm [4308M-101-222]	2.2 kOhm [4310M-102-222]	2.2 kOhm [4604X-101-222LF]	2.2 kOhm [4608M-101-222LF]
2.2 kOhm [4308M-101-222LF]	2.2 kOhm [4310M-102-222LF]	2.2 kOhm [4604X-102-222LF]	2.2 kOhm [4608M-102-222LF]
2.2 kOhm [4308M-102-222]	2.2 kOhm [4310R-101-222]	2.2 kOhm [4605M-101-222LF]	2.2 kOhm [4608X-101-222LF]

Multisim 14.1 Education Components

2.2 kOhm [4608X-102-222LF]	2.2 kOhm [4612X-101-222LF]	2.2 kOhm [4816P-2-222LF]	2.2 kOhm [CAT16-222J4LF]
2.2 kOhm [4608X-AP1-222LF]	2.2 kOhm [4612X-102-222LF]	2.2 kOhm [4816P-T01-222]	2.2 kOhm [CAT16-222J8LF]
2.2 kOhm [4608X-AP2-222LF]	2.2 kOhm [4613X-101-222LF]	2.2 kOhm [4816P-T01-222LF]	2.2 kOhm [CAT25-222JALF]
2.2 kOhm [4609H-101-222LF]	2.2 kOhm [4614X-102-222LF]	2.2 kOhm [4816P-T02-222]	2.2 kOhm [CAY10-222J4LF]
2.2 kOhm [4609M-101-222LF]	2.2 kOhm [4814P-1-222]	2.2 kOhm [4816P-T02-222LF]	2.2 kOhm [CAY16-2201F4LF]
2.2 kOhm [4609X-101-222LF]	2.2 kOhm [4814P-1-222LF]	2.2 kOhm [4818P-T02-222]	2.2 kOhm [CAY16-222J4GLF]
2.2 kOhm [4609X-AP1-222LF]	2.2 kOhm [4814P-2-222]	2.2 kOhm [4820P-1-222]	2.2 kOhm [CAY16-222J4LF]
2.2 kOhm [4610H-101-222LF]	2.2 kOhm [4814P-2-222LF]	2.2 kOhm [4820P-2-222]	2.2 kOhm [CAY16-222J8LF]
2.2 kOhm [4610H-102-222LF]	2.2 kOhm [4814P-T01-222]	2.2 kOhm [4820P-2-222LF]	2.2 kOhm [CAY17-222JALF]
2.2 kOhm [4610M-101-222LF]	2.2 kOhm [4814P-T01-222LF]	2.2 kOhm [4820P-T01-222]	2.2 kOhm [CR0402-FX-2201GLF]
2.2 kOhm [4610X-101-222LF]	2.2 kOhm [4814P-T02-222]	2.2 kOhm [4820P-T01-222LF]	2.2 kOhm [CR0402-JW-222GLF]
2.2 kOhm [4610X-102-222LF]	2.2 kOhm [4814P-T02-222LF]	2.2 kOhm [4820P-T02-222]	2.2 kOhm [CR0603-FX-2201ELF]
2.2 kOhm [4610X-AP1-222LF]	2.2 kOhm [4816P-1-222]	2.2 kOhm [CAT10-222J4LF]	2.2 kOhm [CR0603-JW-222ELF]
2.2 kOhm [4610X-AP2-222LF]	2.2 kOhm [4816P-1-222LF]	2.2 kOhm [CAT16-2201F4LF]	2.2 kOhm [CR0603-JW-222GLF]
2.2 kOhm [4611X-101-222LF]	2.2 kOhm [4816P-2-222]	2.2 kOhm [CAT16-222J2LF]	2.2 kOhm [CR0805-FX-2201ELF]

Multisim 14.1 Education Components

2.2 kOhm [CR0805-JW-222ELF]	2.2 kOhm [PWR163S-25-2201FE]	2.2 mH [SRR0906-222YL]	2.2 MOhm [4606X-102-225LF]
2.2 kOhm [CR0805-JW-222GLF]	2.2 kOhm [PWR2615W2201J]	2.2 mH [SRR0908-222YL]	2.2 MOhm [4608X-101-225LF]
2.2 kOhm [CR1206-FX-2201ELF]	2.2 kOhm [PWR2615W2201JE]	2.2 mH [SRR1005-222K]	2.2 MOhm [4608X-102-225LF]
2.2 kOhm [CR1206-JW-222ELF]	2.2 kOhm [PWR4525W2201J]	2.2 mH [SRR1208-222KL]	2.2 MOhm [4609X-101-225LF]
2.2 kOhm [CR2010-FX-2201ELF]	2.2 kOhm [PWR4525W2201JE]	2.2 mH [SRR6603-222ML]	2.2 MOhm [4610X-101-225LF]
2.2 kOhm [CR2010-JW-222ELF]	2.2 kOhm [PWR6327W2201J]	2.2 MOhm [4114R-2-225]	2.2 MOhm [4610X-102-225LF]
2.2 kOhm [CR2512-FX-2201ELF]	2.2 kOhm [PWR6327W2201JE]	2.2 MOhm [4116R-1-225]	2.2 MOhm [4816P-2-225]
2.2 kOhm [CR2512-JW-222ELF]	2.2 mH [SDR0503-222JL]	2.2 MOhm [4116R-1-225LF]	2.2 MOhm [4816P-2-225LF]
2.2 kOhm [CRM1206-FX-2201ELF]	2.2 mH [SDR0805-222KL]	2.2 MOhm [4116R-2-225]	2.2 MOhm [4816P-T01-225]
2.2 kOhm [CRM1206-JW-222ELF]	2.2 mH [SDR0906-222KL]	2.2 MOhm [4306R-102-225]	2.2 MOhm [CAT25-225JALF]
2.2 kOhm [CRM2512-FX-2201ELF]	2.2 mH [SDR1005-222KL]	2.2 MOhm [4308R-102-225]	2.2 MOhm [CHV2512-FX-2204ELF]
2.2 kOhm [CRM2512-JW-222ELF]	2.2 mH [SDR1006-222KL]	2.2 MOhm [4308R-102-225LF]	2.2 MOhm [CR0402-JW-225GLF]
2.2 kOhm [CRT1206-BY-2201ELF]	2.2 mH [SRE6603-222M]	2.2 MOhm [4310R-101-225LF]	2.2 MOhm [CR0603-JW-225ELF]
	2.2 mH [SRR0604-222KL]	2.2 MOhm [4605X-101-225LF]	2.2 MOhm [CR0805-FX-2204ELF]
		2.2 MOhm [4606X-101-225LF]	

Multisim 14.1 Education Components

2.2 MOhm [CR0805-JW- 225ELF]	2.2 nF [C0603C222K1HACT U]	2.2 nF [C0805C222K1GACT U]	2.2 nF [C1206C222K1RACT U]
2.2 MOhm [CR1206-FW- 2204ELF]	2.2 nF [C0603C222K1RACT U]	2.2 nF [C0805C222K1HACT U]	2.2 nF [C1206C222K2RACT U]
2.2 MOhm [CR1206-JW- 225ELF]	2.2 nF [C0603C222K2RACT U]	2.2 nF [C0805C222K1RACT U]	2.2 nF [C1206C222K4RACT U]
2.2 MOhm [CR1206-JW- 225GLF]	2.2 nF [C0603C222K3GACT U]	2.2 nF [C0805C222K2RACT U]	2.2 nF [C1206C222K5GACT U]
2.2 nF [03063C222KAT2A]	2.2 nF [C0603C222K3HACT U]	2.2 nF [C0805C222K3GACT U]	2.2 nF [C1206C222K5RACT U]
2.2 nF [0306YC222KAT2A]	2.2 nF [C0603C222K3RACT U]	2.2 nF [C0805C222K3HACT U]	2.2 nF [C1210C222K1GACT U]
2.2 nF [0306ZC222KAT2A]	2.2 nF [C0603C222K4RACT U]	2.2 nF [C0805C222K3RACT U]	2.2 nF [C1210C222K1RACT U]
2.2 nF [06125C222KAT2V]	2.2 nF [C0603C222K5HACT U]	2.2 nF [C0805C222K5HACT U]	2.2 nF [C1210C222K2GACT U]
2.2 nF [C0402C222K3RACT U]	2.2 nF [C0603C222K5RACT U]	2.2 nF [C0805C222K5RACT U]	2.2 nF [C1210C222K5GACT U]
2.2 nF [C0402C222K4RACT U]	2.2 nF [C0603C222K8RACT U]	2.2 nF [C0805C222KARACT U]	2.2 nF [C1210C222KCGAC TU]
2.2 nF [C0402C222K5RACT U]	2.2 nF [C0603C222K9RACT U]	2.2 nF [C1206C222K1GACT U]	2.2 nF [C1812C222K2GACT U]

Multisim 14.1 Education Components

2.2 nF [C1812C222KBGAC TU]	2.2 nF [GMC7.3222K100K3 1TR12]	2.2 nF [MMC7.3222K100K 31TR12]	2.2 Ohm [CR0402- J/-2R2GLF]
2.2 nF [C1812C222KDGAC TU]	2.2 nF [GMC7.3222K400K3 1TR12]	2.2 nF [MMC7.3222K250K 31TR12]	2.2 Ohm [CR0603- J/-2R2ELF]
2.2 nF [C1825C222KBGAC TU]	2.2 nF [GMC7.3223K100K3 1TR12]	2.2 nF [MMC7.3222K400K 31TR12]	2.2 Ohm [CR0603- J/-2R2GLF]
2.2 nF [C2220C222KBGAC TU]	2.2 nF [GMC7.3223K250K3 3TR12]	2.2 nF [MMC7.3222K50K3 1TR12]	2.2 Ohm [CR1206- J/-2R2ELF]
2.2 nF [C2225C222KBGAC TU]	2.2 nF [GPC7.3222K160K3 1TR12]	2.2 nF [MMC7.3222K63K3 1TR12]	2.2 Ohm [CR2010- J/-2R2ELF]
2.2 nF [CA064C222K1RACT U]	2.2 nF [GPC7.3222K630K3 3TR12]	2.2 nF [SPC7.3222K100K31 TR12]	2.2 Ohm [CR2512- J/-2R2ELF]
2.2 nF [CA064C222K4RACT U]	2.2 nF [GPC7.3222K63K31 TR12]	2.2 nF [SPC7.3222K250K31 TR12]	2.2 Ohm [CRL0603- FW-2R20ELF]
2.2 nF [CA064C222K5RACT U]	2.2 nF [LD17YC222KAB2S]	2.2 nF [SPC7.3222K400K31 TR12]	2.2 Ohm [CRL0603- JW-2R20ELF]
2.2 nF [GMC5.7222K100J3 1TR12]	2.2 nF [MMC5.7222K100J 31TR12]	2.2 nF [SPC7.3222K630K33 TR12]	2.2 Ohm [CRL0805- FW-2R20ELF]
2.2 nF [GMC5.7222K50J31 TR12]	2.2 nF [MMC5.7222K250J 31TR12]	2.2 nF [W2F15C2228AT1A]	2.2 Ohm [CRL0805- JW-2R20ELF]
2.2 nF [GMC5.7223K250J3 5TR12]	2.2 nF [MMC5.7222K50J3 1TR12]	2.2 nF [W3F15C2228AT1A]	2.2 Ohm [CRL1206- FW-2R20ELF]
			2.2 Ohm [CRL1206- JW-2R20ELF]
			2.2 Ohm [CRL2010- FW-2R20ELF]
			2.2 Ohm [CRL2010- JW-2R20ELF]

Multisim 14.1 Education Components

2.2 Ohm [CRL2512-FW-2R20ELF]	2.2 Ohm [PWR221T-30-2R20J]	2.2 uF [0612ZC225KAT2A]	2.2 uF [C0805C225M4VAC TU]
2.2 Ohm [CRM1206-FX-2R20ELF]	2.2 Ohm [PWR2615W2R20J]	2.2 uF [C0402C225K9PACT U]	2.2 uF [C0805C225M8VAC TU]
2.2 Ohm [CRM1206-JW-2R2ELF]	2.2 Ohm [PWR263S-20-2R20F]	2.2 uF [C0603C225K4PACT U]	2.2 uF [C1206C225K3NAC TU]
2.2 Ohm [CRM2010-JW-2R2ELF]	2.2 Ohm [PWR263S-20-2R20J]	2.2 uF [C0603C225K8PACT U]	2.2 uF [C1206C225K3PACT U]
2.2 Ohm [CRM2512-JW-2R2ELF]	2.2 Ohm [PWR263S-20-2R20JE]	2.2 uF [C0603C225K9PACT U]	2.2 uF [C1206C225K4PACT U]
2.2 Ohm [PWR163S-25-2R20F]	2.2 Ohm [PWR263S-35-2R20J]	2.2 uF [C0805C225K4PACT U]	2.2 uF [C1206C225K4RACT U]
2.2 Ohm [PWR163S-25-2R20J]	2.2 Ohm [PWR3014WA2R20JE]	2.2 uF [C0805C225K4RACT U]	2.2 uF [C1206C225K8PACT U]
2.2 Ohm [PWR163S-25-2R20JE]	2.2 Ohm [PWR4318W2R20JE]	2.2 uF [C0805C225K8PACT U]	2.2 uF [C1206C225K8RACT U]
2.2 Ohm [PWR2010W2R20JE]	2.2 Ohm [PWR4525W2R20J]	2.2 uF [C0805C225K8RACT U]	2.2 uF [C1206C225K9PACT U]
2.2 Ohm [PWR220T-35-2R20J]	2.2 Ohm [PWR6327W2R20F]	2.2 uF [C0805C225K9PACT U]	2.2 uF [C1206C225K9RACT U]
2.2 Ohm [PWR221T-30-2R20F]	2.2 Ohm [PWR6327W2R20J]	2.2 uF [C0805C225K9RACT U]	2.2 uF [C1206C225M4VAC TU]

Multisim 14.1 Education Components

2.2 uF [C1210C225K1RACT U]	2.2 uF [C2220C225K5RACT U]	2.2 uF [MDS15225K100B5 3P3TUBE]	2.2 uF [T491B225M035AT]
2.2 uF [C1210C225K3PACT U]	2.2 uF [C2225C225K5RACT U]	2.2 uF [PGC24D225MAB2S 1]	2.2 uF [T491C225M025AT]
2.2 uF [C1210C225K3RACT U]	2.2 uF [C2225C225M5UAC TU]	2.2 uF [T409C225M015AH 4250]	2.2 uF [T491C225M050AT]
2.2 uF [C1210C225K4RACT U]	2.2 uF [LD186C225KAB2A]	2.2 uF [T429A225M010AH 4250]	2.2 uF [T491D225M050AT]
2.2 uF [C1210C225K5RACT U]	2.2 uF [LD18ZC225KAB2A]	2.2 uF [T429C225M015AH 4250]	2.2 uF [T491S225M016AT]
2.2 uF [C1210C225K8RACT U]	2.2 uF [LGC24D225MAT2S 1]	2.2 uF [T491A225M006AT]	2.2 uF [T494A225M006AT]
2.2 uF [C1210C225K9PACT U]	2.2 uF [MDC10225K100A5 2P3TUBE]	2.2 uF [T491A225M010AT]	2.2 uF [T494A225M010AT]
2.2 uF [C1210C225K9RACT U]	2.2 uF [MDC10225K50A52 P3TUBE]	2.2 uF [T491A225M016AT]	2.2 uF [T494A225M016AT]
2.2 uF [C1210C225K9RACT U]	2.2 uF [MDC15225K100B5 3P3TUBE]	2.2 uF [T491A225M020AT]	2.2 uF [T494A225M020AT]
2.2 uF [C1210C225M8VAC TU]	2.2 uF [MDC15225K50B53 P3TUBE]	2.2 uF [T491A225M025AT]	2.2 uF [T494B225M020AT]
2.2 uF [C1812C225K1RACT U]	2.2 uF [MDK10225K50A52 P3TUBE]	2.2 uF [T491B225M010AT]	2.2 uF [T494B225M025AT]
2.2 uF [C1825C225K5RACT U]	2.2 uF [MDS10225K50A52 P3TUBE]	2.2 uF [T491B225M020AT]	2.2 uF [T494B225M035AT]
		2.2 uF [T491B225M025AT]	2.2 uF [T494C225M025AT]
			2.2 uF [T494C225M035AT]

Multisim 14.1 Education Components

2.2 uF [T494C225M050AT]	2.2 uF [TAJA225K035RNJ]	2.2 uF [TAJS225K010RNJ]	2.2 uF [TPSA225K025R2500]
2.2 uF [T494D225M050AT]	2.2 uF [TAJB225K016RNJ]	2.2 uF [TAJS225K016RNJ]	2.2 uF [TPSB225K025R1200]
2.2 uF [T494S225M016AT]	2.2 uF [TAJB225K020RNJ]	2.2 uF [TAJS225K020RNJ]	2.2 uF [TPSB225K025R2500]
2.2 uF [T498A225M010AT E4K6]	2.2 uF [TAJB225K025RNJ]	2.2 uF [TAJT225K016RNJ]	2.2 uF [TPSB225K035R2000]
2.2 uF [T498B225M025AT E3K0]	2.2 uF [TAJC225K035RNJ]	2.2 uF [TAJT225K020RNJ]	2.2 uF [TPSC225K035R1000]
2.2 uF [TACL225K003RTA]	2.2 uF [TAJC225K050RNJ]	2.2 uF [TAJT225K035RNJ]	2.2 uF [TPSC225K050R1500]
2.2 uF [TACL225K004RTA]	2.2 uF [TAJD225K050RNJ]	2.2 uF [THJA225K016RJN]	2.2 uF [TPSD225K050R1200]
2.2 uF [TACL225K006RTA]	2.2 uF [TAJP225K020RNJ]	2.2 uF [THJB225K025RJN]	2.2 uF [TPSD225K050R1200]
2.2 uF [TACL225K010RTA]	2.2 uF [TAJR225K004RNJ]	2.2 uF [THJC225K035RJN]	2.2 uF [TPSR225K006R7000]
2.2 uF [TAJA225K006RNJ]	2.2 uF [TAJR225K006RNJ]	2.2 uF [TPSA225K010R1800]	2.2 uF [TPST225K016R2000]
2.2 uF [TAJA225K010RNJ]	2.2 uF [TAJR225K010RNJ]	2.2 uF [TPSA225K016R1800]	2.2 uF [TRJA225K016RRJ]
2.2 uF [TAJA225K016RNJ]	2.2 uF [TAJR225K016RNJ]	2.2 uF [TPSA225K016R3500]	2.2 uF [TRJA225K025RRJ]
2.2 uF [TAJA225K020RNJ]	2.2 uF [TAJS225K004RNJ]	2.2 uF [TPSA225K020R3000]	2.2 uF [TRJD225K050R1200]
2.2 uF [TAJA225K025RNJ]	2.2 uF [TAJS225K006RNJ]		

Multisim 14.1 Education Components

2.2 uH [SDE0403A-2R2M]	2.2 uH [SDR7045-2R2M]	2.2 uH [SRP1038A-2R2M]	2.2 uH [SRP6540-2R2M]
2.2 uH [SDE0604A-2R2M]	2.2 uH [SRN2010-2R2M]	2.2 uH [SRP1040-2R2M]	2.2 uH [SRP7028A-2R2M]
2.2 uH [SDE1006A-2R2M]	2.2 uH [SRN2012-2R2M]	2.2 uH [SRP1045-2R2M]	2.2 uH [SRP7030-2R2FM]
2.2 uH [SDR0302-2R2ML]	2.2 uH [SRN2510-2R2M]	2.2 uH [SRP1206-2R0Y]	2.2 uH [SRP7050TA-2R2M]
2.2 uH [SDR0403-2R2ML]	2.2 uH [SRN2512-2R2M]	2.2 uH [SRP1235-2R2M]	2.2 uH [SRR0604-2R2ML]
2.2 uH [SDR0604-2R2ML]	2.2 uH [SRN3010-2R2M]	2.2 uH [SRP1250-2R2M]	2.2 uH [SRR0618-2R2ML]
2.2 uH [SDR0703-2R2ML]	2.2 uH [SRN3015-2R2M]	2.2 uH [SRP1265A-2R2M]	2.2 uH [SRR0805-2R2M]
2.2 uH [SDR0906-2R2ML]	2.2 uH [SRN4012T-2R2M]	2.2 uH [SRP1270-2R2M]	2.2 uH [SRR1003-2R2M]
2.2 uH [SDR1005-2R2ML]	2.2 uH [SRN4018-2R2M]	2.2 uH [SRP1770TA-2R2M]	2.2 uH [SRR1005-2R2M]
2.2 uH [SDR1006-2R2ML]	2.2 uH [SRN4026-2R2Y]	2.2 uH [SRP4012TA-2R2M]	2.2 uH [SRR1210-2R2Y]
2.2 uH [SDR1307-2R2ML]	2.2 uH [SRN5020-2R2Y]	2.2 uH [SRP4020-2R2M]	2.2 uH [SRR1210A-2R2Y]
2.2 uH [SDR1307A-2R2M]	2.2 uH [SRN5040-2R2Y]	2.2 uH [SRP4020TA-2R2M]	2.2 uH [SRR1260-2R2Y]
2.2 uH [SDR1806-2R2ML]	2.2 uH [SRN6028-2R2Y]	2.2 uH [SRP5015TA-2R2M]	2.2 uH [SRR1260A-2R2Y]
2.2 uH [SDR6603-2R2M]	2.2 uH [SRN6045-2R2Y]	2.2 uH [SRP5030T-2R2M]	2.2 uH [SRR4011-2R2YL]
2.2 uH [SDR7030-2R2M]	2.2 uH [SRN8040-2R2Y]	2.2 uH [SRP5030TA-2R2M]	2.2 uH [SRR4018-2R2Y]

Multisim 14.1 Education Components

2.2 uH [SRR4028-2R2Y]	2.2 uH [SRU3011-2R2Y]	2.21 kOhm [CR1206-FX-2211ELF]	2.26 kOhm [CR0805-FX-2261ELF]
2.2 uH [SRR6603-2R2ML]	2.2 uH [SRU3017-2R2Y]	2.21 kOhm [CRM1206-FX-2211ELF]	2.26 kOhm [CR1206-FX-2261ELF]
2.2 uH [SRR7032-2R2M]	2.2 uH [SRU5018-2R2Y]	2.21 kOhm [CRT0603-BY-2211ELF]	2.26 kOhm [CRT0402-FZ-2261GLF]
2.2 uH [SRR7045-2R2M]	2.2 uH [SRU5028-2R2Y]	2.21 kOhm [CRT0603-CW-2211ELF]	2.26 kOhm [CRT0603-CY-2261ELF]
2.2 uH [SRU1028-2R2Y]	2.2 uH [SRU5028A-2R2Y]	2.21 kOhm [CRT0603-CY-2211ELF]	2.26 kOhm [CRT0805-BY-2261ELF]
2.2 uH [SRU1028A-2R2Y]	2.2 uH [SRU6025-2R2Y]	2.21 kOhm [CRT0805-FX-2211ELF]	2.26 kOhm [CRT0805-FV-2261ELF]
2.2 uH [SRU1038-2R2Y]	2.2 uH [SRU6025A-2R2Y]	2.21 kOhm [CR0805-FX-2214ELF]	2.3 kOhm [4116R-1-232]
2.2 uH [SRU1038A-2R2Y]	2.2 uH [SRU8043-2R2Y]	2.21 Ohm [CRM1206-FX-2R21ELF]	2.32 kOhm [CR0402-FX-2321GLF]
2.2 uH [SRU1048-2R2Y]	2.21 kOhm [CAT16-2211F4LF]	2.26 kOhm [CR0402-FX-2261GLF]	2.32 kOhm [CR0603-FX-2321ELF]
2.2 uH [SRU1048A-2R2Y]	2.21 kOhm [CAY16-2211F4LF]	2.26 kOhm [CR0603-FX-2211GLF]	2.32 kOhm [CR0805-FX-2321ELF]
2.2 uH [SRU1063-2R2Y]	2.21 kOhm [CR0402-FX-2211GLF]		
2.2 uH [SRU2009-2R2Y]	2.21 kOhm [CR0603-FX-2211ELF]		
2.2 uH [SRU2011-2R2Y]	2.21 kOhm [CR0603-FX-2211GLF]		
2.2 uH [SRU2013-2R2Y]	2.21 kOhm [CR0805-FX-2211ELF]		
2.2 uH [SRU2016-2R2Y]			

Multisim 14.1 Education Components

2.32 kOhm [CR1206-FX- 2321ELF]	2.4 kOhm [4116R- 1-242LF]	2.4 kOhm [CRM1206-JW- 242ELF]	2.4 nF [C0603C242K5HACT U]
2.32 kOhm [CRT0805-BX- 2321ELF]	2.4 kOhm [CAT16- 2401F4LF]	2.4 kOhm [CRM2010-JW- 242ELF]	2.4 nF [C0805C242K1GACT U]
2.37 kOhm [CAY16- 2371F4LF]	2.4 kOhm [CAT16- 242J4LF]	2.4 kOhm [CRT0805-BV- 2401ELF]	2.4 nF [C0805C242K1HACT U]
2.37 kOhm [CR0402-FX- 2371GLF]	2.4 kOhm [CAY16- 242J4LF]	2.4 kOhm [CRT0805-BW- 2401ELF]	2.4 nF [C0805C242K3HACT U]
2.37 kOhm [CR0603-FX- 2371ELF]	2.4 kOhm [CR0402- FX-2401GLF]	2.4 kOhm [CRT0805-FV- 2401ELF]	2.4 nF [C0805C242K5HACT U]
2.37 kOhm [CR0805-FX- 2371ELF]	2.4 kOhm [CR0402- JW-242GLF]	2.4 MOhm [4116R- 1-245LF]	2.4 nF [C1825C242KBGAC TU]
2.37 kOhm [CR1206-FX- 2371ELF]	2.4 kOhm [CR0603- JW-242ELF]	2.4 MOhm [CR0603-JW- 245ELF]	2.4 nF [C2220C242KBGAC TU]
2.37 kOhm [CR2512-FX- 2371ELF]	2.4 kOhm [CR0805- FX-2401ELF]	2.4 MOhm [CR0805-JW- 245ELF]	2.4 nF [C2225C242KBGAC TU]
2.37 kOhm [CRT0402-FZ- 2371GLF]	2.4 kOhm [CR0805- JW-242ELF]	2.4 MOhm [CR1206-JW- 245ELF]	2.4 Ohm [CR0603- J/-2R4ELF]
2.4 kOhm [4114R- 1-242]	2.4 kOhm [CR1206- FX-2401ELF]	2.4 nF [C0603C242K1HACT U]	2.4 Ohm [CR0805- J/-2R4ELF]
2.4 kOhm [4114R- 1-242LF]	2.4 kOhm [CR1206- JW-242ELF]	2.4 nF [C0603C242K3HACT U]	2.4 Ohm [CR1206- J/-2R4ELF]
2.4 kOhm [4116R- 1-242]	2.4 kOhm [CR2010- JW-242ELF]		2.4 Ohm [CR2010- J/-2R4ELF]

Multisim 14.1 Education Components

2.4 Ohm [CRL0603-FW-2R40ELF]	2.4 uH [SRR1280-2R4Y]	2.49 kOhm [CRT0603-BV-2491ELF]	2.5 Ohm [PWR163S-25-2R50F]
2.4 Ohm [CRL0603-JW-2R40ELF]	2.43 kOhm [CR0402-FX-2431GLF]	2.49 kOhm [CRT0603-BY-2491ELF]	2.5 Ohm [PWR163S-25-2R50J]
2.4 Ohm [CRL0805-FW-2R40ELF]	2.43 kOhm [CR0603-FX-2431ELF]	2.49 kOhm [CRT0603-CY-2491ELF]	2.5 Ohm [PWR220T-20-2R50F]
2.4 Ohm [CRL0805-JW-2R40ELF]	2.43 kOhm [CR0805-FX-2431ELF]	2.49 kOhm [CRT0805-BV-2491ELF]	2.5 Ohm [PWR220T-20-2R50J]
2.4 Ohm [CRL1206-FW-2R40ELF]	2.43 kOhm [CR1206-FX-2431ELF]	2.5 kOhm [4108R-1-252]	2.5 Ohm [PWR220T-35-2R50F]
2.4 Ohm [CRL1206-JW-2R40ELF]	2.49 kOhm [CAT16-2491F4LF]	2.5 kOhm [4108R-1-252LF]	2.5 Ohm [PWR221T-30-2R50F]
2.4 Ohm [CRL2010-FW-2R40ELF]	2.49 kOhm [CR0201-FW-2491GLF]	2.5 kOhm [4116R-1-252]	2.5 Ohm [PWR263S-20-2R50F]
2.4 Ohm [CRL2512-FW-2R40ELF]	2.49 kOhm [CR0402-FX-2491GLF]	2.5 kOhm [PWR220T-35-2501F]	2.5 Ohm [PWR263S-20-2R50J]
2.4 Ohm [CRM2512-JW-2R4ELF]	2.49 kOhm [CR0603-FX-2491ELF]	2.5 kOhm [PWR220T-35-2501J]	2.5 Ohm [PWR263S-35-2R50F]
2.4 Ohm [PWR263S-35-2R40J]	2.49 kOhm [CR0805-FX-2491ELF]	2.5 kOhm [PWR263S-35-2501F]	2.5 Ohm [PWR263S-35-2R50J]
2.4 uH [SRR1240-2R4Y]	2.49 kOhm [CR1206-FX-2491ELF]	2.5 kOhm [PWR6327W2501J]	2.5 uH [SDE0805A-2R5M]
2.4 uH [SRR1260-2R4Y]	2.49 kOhm [CR2010-FX-2491ELF]		2.5 uH [SDR0603-2R5ML]

Multisim 14.1 Education Components

2.5 uH [SDR0805-2R5ML]	2.5 uH [SRU8028-2R5Y]	2.61 kOhm [CR1206-FX-2611ELF]	2.7 kOhm [4114R-2-272]
2.5 uH [SDR1005-2R5ML]	2.5 uH [SRU8028A-2R5Y]	2.61 kOhm [CRM1206-FX-2611ELF]	2.7 kOhm [4114R-2-272LF]
2.5 uH [SDR1305-2R5Y]	2.55 kOhm [CR0402-FX-2551GLF]	2.61 kOhm [CRT0402-FZ-2611GLF]	2.7 kOhm [4116R-1-272]
2.5 uH [SRP1040-2R5M]	2.55 kOhm [CR0603-FX-2551ELF]	2.61 kOhm [CRT0603-FY-2611ELF]	2.7 kOhm [4116R-2-272]
2.5 uH [SRP7028A-2R5M]	2.55 kOhm [CR0805-FX-2551ELF]	2.61 kOhm [CRT0805-CX-2611ELF]	2.7 kOhm [4116R-2-272LF]
2.5 uH [SRR0603-2R5ML]	2.55 kOhm [CR1206-FX-2551ELF]	2.61 Ohm [CRM1206-FX-2R61ELF]	2.7 kOhm [4306M-101-272]
2.5 uH [SRR0604-2R5ML]	2.55 kOhm [CR2010-FX-2551ELF]	2.67 kOhm [CR0402-FX-2671GLF]	2.7 kOhm [4306M-102-272]
2.5 uH [SRR1205-2R5ML]	2.55 kOhm [CRT0603-FY-2551ELF]	2.67 kOhm [CR0603-FX-2671ELF]	2.7 kOhm [4306M-102-272LF]
2.5 uH [SRR1206-2R5ML]	2.6 uH [SRR5028-2R6Y]	2.67 kOhm [CR0805-FX-2671ELF]	2.7 kOhm [4306R-101-272]
2.5 uH [SRR1208-2R5ML]	2.61 kOhm [CR0402-FX-2611GLF]	2.67 kOhm [CR1206-FX-2671ELF]	2.7 kOhm [4306R-101-272LF]
2.5 uH [SRR3011-2R5YL]	2.61 kOhm [CR0603-FX-2611ELF]	2.7 kOhm [4114R-1-272]	2.7 kOhm [4306R-102-272LF]
2.5 uH [SRR5018-2R5Y]	2.61 kOhm [CR0805-FX-2611ELF]	2.7 kOhm [4114R-1-272LF]	
2.5 uH [SRR6028-2R5Y]			
2.5 uH [SRU1038-2R5Y]			
2.5 uH [SRU5011-2R5Y]			

Multisim 14.1 Education Components

2.7 kOhm [4308H-101-272LF]	2.7 kOhm [4310R-101-272LF]	2.7 kOhm [4608H-101-272LF]	2.7 kOhm [4610X-AP2-272LF]
2.7 kOhm [4308M-102-272]	2.7 kOhm [4310R-102-272]	2.7 kOhm [4608H-102-272LF]	2.7 kOhm [4611X-101-272LF]
2.7 kOhm [4308M-102-272LF]	2.7 kOhm [4310R-102-272LF]	2.7 kOhm [4608X-101-272LF]	2.7 kOhm [4614X-102-272LF]
2.7 kOhm [4308R-101-272]	2.7 kOhm [4416P-2-272]	2.7 kOhm [4608X-102-272LF]	2.7 kOhm [4814P-1-272]
2.7 kOhm [4308R-101-272LF]	2.7 kOhm [4420P-2-272]	2.7 kOhm [4608X-AP2-272LF]	2.7 kOhm [4814P-1-272LF]
2.7 kOhm [4308R-102-272]	2.7 kOhm [4420P-T02-272]	2.7 kOhm [4609H-101-272LF]	2.7 kOhm [4814P-2-272]
2.7 kOhm [4308R-102-272LF]	2.7 kOhm [4604X-101-272LF]	2.7 kOhm [4609M-101-272LF]	2.7 kOhm [4814P-2-272LF]
2.7 kOhm [4309R-101-272]	2.7 kOhm [4604X-102-272LF]	2.7 kOhm [4609X-101-272LF]	2.7 kOhm [4814P-T01-272]
2.7 kOhm [4309R-101-272LF]	2.7 kOhm [4605X-101-272LF]	2.7 kOhm [4609X-AP1-272LF]	2.7 kOhm [4814P-T01-272LF]
2.7 kOhm [4310H-101-272]	2.7 kOhm [4606H-101-272LF]	2.7 kOhm [4610H-101-272LF]	2.7 kOhm [4814P-T02-272]
2.7 kOhm [4310H-101-272LF]	2.7 kOhm [4606M-102-272LF]	2.7 kOhm [4610H-102-272LF]	2.7 kOhm [4814P-T02-272LF]
2.7 kOhm [4310M-101-272]	2.7 kOhm [4606X-101-272LF]	2.7 kOhm [4610M-101-272LF]	2.7 kOhm [4816P-1-272]
2.7 kOhm [4310M-101-272LF]	2.7 kOhm [4606X-102-272LF]	2.7 kOhm [4610X-101-272LF]	2.7 kOhm [4816P-1-272LF]
2.7 kOhm [4310M-102-272]	2.7 kOhm [4606X-AP1-272LF]	2.7 kOhm [4610X-102-272LF]	2.7 kOhm [4816P-2-272]
2.7 kOhm [4310R-101-272]	2.7 kOhm [4607X-101-272LF]	2.7 kOhm [4610X-AP1-272LF]	2.7 kOhm [4816P-2-272LF]

Multisim 14.1 Education Components

2.7 kOhm [4816P-T01-272]	2.7 kOhm [CAY17-272JALF]	2.7 kOhm [CRM1206-FX-2701ELF]	2.7 mH [SDR1006-272KL]
2.7 kOhm [4816P-T01-272LF]	2.7 kOhm [CR0201-FW-2701GLF]	2.7 kOhm [CRM1206-JW-272ELF]	2.7 mH [SRR0906-272YL]
2.7 kOhm [4816P-T02-272]	2.7 kOhm [CR0402-FX-2701GLF]	2.7 kOhm [CRM2512-JW-272ELF]	2.7 mH [SRR1005-272K]
2.7 kOhm [4816P-T02-272LF]	2.7 kOhm [CR0402-JW-272GLF]		2.7 mH [SRR1208-272KL]
2.7 kOhm [4820P-2-272]	2.7 kOhm [CR0603-FX-2701ELF]	2.7 kOhm [CRT0603-BX-2701ELF]	2.7 MOhm [4116R-1-275]
2.7 kOhm [4820P-T02-272]	2.7 kOhm [CR0603-FX-2701HLF]	2.7 kOhm [CRT0603-BY-2701ELF]	2.7 MOhm [4116R-1-275LF]
2.7 kOhm [CAT10-272J4LF]	2.7 kOhm [CR0603-JW-272ELF]	2.7 kOhm [CRT0805-FX-2701ELF]	2.7 MOhm [CAT25-275JALF]
2.7 kOhm [CAT16-2701F4LF]	2.7 kOhm [CR0603-JW-272GLF]	2.7 kOhm [CRT1206-BY-2701ELF]	2.7 MOhm [CR0603-JW-275ELF]
2.7 kOhm [CAT16-272J4LF]	2.7 kOhm [CR0805-FX-2701ELF]	2.7 kOhm [PWR2615W2701F]	2.7 MOhm [CR1206-JW-275ELF]
2.7 kOhm [CAT16-272J8LF]	2.7 kOhm [CR0805-JW-272ELF]	2.7 kOhm [PWR2615W2701J]	2.7 nF [C0402C272K3RACTU]
2.7 kOhm [CAT25-272JALF]	2.7 kOhm [CR0805-JW-272GLF]	2.7 mF [2R5SVPC2700M]	2.7 nF [C0402C272K4RACTU]
2.7 kOhm [CAY10-272J4LF]	2.7 kOhm [CR1206-FX-2701ELF]	2.7 mH [SDR0503-272JL]	2.7 nF [C0402C272K5RACTU]
2.7 kOhm [CAY16-2701F4LF]	2.7 kOhm [CR1206-JW-272ELF]	2.7 mH [SDR0805-272KL]	
2.7 kOhm [CAY16-272J4LF]	2.7 kOhm [CR1206-JW-272GLF]	2.7 mH [SDR0906-272KL]	
2.7 kOhm [CAY16-272J8LF]	2.7 kOhm [CR2512-JW-272ELF]		

Multisim 14.1 Education Components

2.7 nF [C0603C272K1HACT U]	2.7 nF [C0805C272K1RACT U]	2.7 nF [C1206C272K1RACT U]	2.7 nF [C2225C272KBGAC TU]
2.7 nF [C0603C272K1RACT U]	2.7 nF [C0805C272K2RACT U]	2.7 nF [C1206C272K2RACT U]	2.7 nF [GMC5.7272K100J3 1TR12]
2.7 nF [C0603C272K3GACT U]	2.7 nF [C0805C272K3GACT U]	2.7 nF [C1206C272K5GACT U]	2.7 nF [GMC5.7272K50J31 TR12]
2.7 nF [C0603C272K3HACT U]	2.7 nF [C0805C272K3HACT U]	2.7 nF [C1206C272K5RACT U]	2.7 nF [GMC5.7273K100J3 3TR12]
2.7 nF [C0603C272K3RACT U]	2.7 nF [C0805C272K3RACT U]	2.7 nF [C1210C272K2GACT U]	2.7 nF [GMC7.3272K100K3 1TR12]
2.7 nF [C0603C272K4RACT U]	2.7 nF [C0805C272K4GACT U]	2.7 nF [C1210C272K5GACT U]	2.7 nF [GMC7.3272K400K3 1TR12]
2.7 nF [C0603C272K5HACT U]	2.7 nF [C0805C272K4RACT U]	2.7 nF [C1210C272KCGAC TU]	2.7 nF [GMC7.3273K100K3 1TR12]
2.7 nF [C0603C272K5RACT U]	2.7 nF [C0805C272K5HACT U]	2.7 nF [C1812C272K1GACT U]	2.7 nF [GMC7.3273K250K3 5TR12]
2.7 nF [C0603C272K8RACT U]	2.7 nF [C0805C272K5RACT U]	2.7 nF [C1812C272K5GACT U]	2.7 nF [MMC5.7272K100J 31TR12]
2.7 nF [C0805C272K1GACT U]	2.7 nF [C0805C272KARACT U]	2.7 nF [C1825C272KBGAC TU]	2.7 nF [MMC5.7272K250J 31TR12]
2.7 nF [C0805C272K1HACT U]	2.7 nF [C1206C272K1GACT U]	2.7 nF [C2220C272KBGAC TU]	2.7 nF [MMC5.7272K50J3 1TR12]

Multisim 14.1 Education Components

2.7 nF [MMC7.3272K100K 31TR12]	2.7 Ohm [CRL0805- JW-2R70ELF]	2.7 uF [C1206C275K4RACT U]	2.7 uH [SDE0604A- 2R7M]
2.7 nF [MMC7.3272K250K 31TR12]	2.7 Ohm [CRL1206- FW-2R70ELF]	2.7 uF [C1206C275K8RACT U]	2.7 uH [SDR0302- 2R7ML]
2.7 nF [MMC7.3272K400K 31TR12]	2.7 Ohm [CRL1206- JW-2R70ELF]	2.7 uF [C1206C275K9PACT U]	2.7 uH [SDR0403- 2R7ML]
2.7 nF [MMC7.3272K50K3 1TR12]	2.7 Ohm [CRL2010- JW-2R70ELF]	2.7 uF [C1206C275K9RACT U]	2.7 uH [SDR0604- 2R7ML]
2.7 nF [MMC7.3272K63K3 1TR12]	2.7 Ohm [CRL2512- FW-2R70ELF]	2.7 uF [MDC10275K100A5 2P3TUBE]	2.7 uH [SDR0703- 2R7ML]
2.7 Ohm [CR0402- J/-2R7GLF]	2.7 Ohm [CRM1206-JW- 2R7ELF]	2.7 uF [MDC10275K50A52 P3TUBE]	2.7 uH [SDR0906- 2R7ML]
2.7 Ohm [CR0603- J/-2R7ELF]	2.7 Ohm [CRM2512-JW- 2R7ELF]	2.7 uF [MDC15275K100B5 3P3TUBE]	2.7 uH [SDR1030- 2R7M]
2.7 Ohm [CR0805- J/-2R7ELF]	2.7 Ohm [PWR5322W2R70JE]	2.7 uF [MDC15275K50B53 P3TUBE]	2.7 uH [SDR1045- 2R7M]
2.7 Ohm [CR1206- J/-2R7ELF]	2.7 Ohm [PWR6327N2R70JE]	2.7 uF [MDK15275K100B5 3P3TUBE]	2.7 uH [SDR1307- 2R7ML]
2.7 Ohm [CR2010- J/-2R7ELF]	2.7 uF [C0805C275K8PACT U]	2.7 uF [MDK15275K50B53 P3TUBE]	2.7 uH [SDR1307A- 2R7M]
2.7 Ohm [CRL0603- FW-2R70ELF]	2.7 uF [C1206C275K3PACT U]	2.7 uF [MDS15275K50B53 P3TUBE]	2.7 uH [SRP1205- 2R5Y]
2.7 Ohm [CRL0603- JW-2R70ELF]	2.7 uF [C1206C275K4PACT U]		2.7 uH [SRP1250- 2R7M]
2.7 Ohm [CRL0805- FW-2R70ELF]			2.7 uH [SRR0906- 2R7ML]
			2.7 uH [SRR0908- 2R7ML]

Multisim 14.1 Education Components

2.7 uH [SRR1305-2R7ZL]	2.8 kOhm [CR0603-FX-2801ELF]	2.87 kOhm [CRT0805-BY-2871ELF]	20 kOhm [4116R-1-203]
2.7 uH [SRR4018-2R7Y]	2.8 kOhm [CR0805-FX-2801ELF]	2.9 kOhm [4308M-102-292]	20 kOhm [4116R-1-203LF]
2.7 uH [SRR4028-2R7Y]	2.8 kOhm [CR1206-FX-2801ELF]	2.9 kOhm [4308M-102-292LF]	20 kOhm [4116R-2-203]
2.7 uH [SRR7045-2R7M]	2.8 kOhm [CRT0402-BY-2801GLF]	2.94 kOhm [CR0402-FX-2941GLF]	20 kOhm [4116R-2-203LF]
2.7 uH [SRU6011-2R7Y]	2.8 kOhm [CRT0805-BX-2801ELF]	2.94 kOhm [CR0603-FX-2941ELF]	20 kOhm [4306M-101-203]
2.74 kOhm [CR0402-FX-2741GLF]	2.8 kOhm [CRT0805-BY-2801ELF]	2.94 kOhm [CR0805-FX-2941ELF]	20 kOhm [4306M-101-203LF]
2.74 kOhm [CR0603-FX-2741ELF]	2.8 Ohm [PWR6327N2R80FE]	2.94 kOhm [CR1206-FX-2941ELF]	20 kOhm [4306R-101-203]
2.74 kOhm [CR0805-FX-2741ELF]	2.87 kOhm [CR0402-FX-2871GLF]	2 AMP	20 kOhm [4306R-102-203LF]
2.74 kOhm [CR1206-FX-2741ELF]	2.87 kOhm [CR0603-FX-2871ELF]	20 kOhm [4108R-1-203]	20 kOhm [4308M-102-203]
2.74 kOhm [CR2010-FX-2741ELF]	2.87 kOhm [CR0805-FX-2871ELF]	20 kOhm [4108R-1-203LF]	20 kOhm [4308M-102-203LF]
2.74 kOhm [CRT0603-BX-2741ELF]	2.87 kOhm [CR1206-FX-2871ELF]	20 kOhm [4114R-1-203]	20 kOhm [4308R-101-203]
2.74 kOhm [CRT0603-BY-2741ELF]	2.87 kOhm [CRT0402-FZ-2871GLF]	20 kOhm [4114R-1-203LF]	20 kOhm [4308R-101-203LF]
2.8 kOhm [CR0402-FX-2801GLF]		20 kOhm [4114R-2-203]	20 kOhm [4308R-102-203]

Multisim 14.1 Education Components

20 kOhm [4308R-102-203LF]	20 kOhm [4420P-2-203]	20 kOhm [4608X-102-203LF]	20 kOhm [4814P-2-203LF]
20 kOhm [4309R-101-203]	20 kOhm [4420P-2-203LF]	20 kOhm [4608X-AP1-203LF]	20 kOhm [4814P-T01-203]
20 kOhm [4309R-101-203LF]	20 kOhm [4420P-T02-203]	20 kOhm [4608X-AP2-203LF]	20 kOhm [4814P-T01-203LF]
20 kOhm [4310M-101-203]	20 kOhm [4604X-101-203LF]	20 kOhm [4609M-101-203LF]	20 kOhm [4814P-T02-203]
20 kOhm [4310M-101-203LF]	20 kOhm [4604X-102-203LF]	20 kOhm [4609X-101-203LF]	20 kOhm [4814P-T02-203LF]
20 kOhm [4310R-101-203]	20 kOhm [4605X-101-203LF]	20 kOhm [4609X-AP1-203LF]	20 kOhm [4816P-1-203]
20 kOhm [4310R-101-203LF]	20 kOhm [4606H-102-203LF]	20 kOhm [4610H-101-203LF]	20 kOhm [4816P-1-203F]
20 kOhm [4310R-102-203]	20 kOhm [4606X-101-203LF]	20 kOhm [4610X-101-203LF]	20 kOhm [4816P-1-203LF]
20 kOhm [4310R-102-203LF]	20 kOhm [4606X-102-203LF]	20 kOhm [4610X-102-203LF]	20 kOhm [4816P-2-203]
20 kOhm [4416P-1-203]	20 kOhm [4606X-AP1-203LF]	20 kOhm [4610X-AP1-203LF]	20 kOhm [4816P-2-203D]
20 kOhm [4416P-1-203LF]	20 kOhm [4606X-AP2-203LF]	20 kOhm [4610X-AP2-203LF]	20 kOhm [4816P-2-203LF]
20 kOhm [4416P-2-203]	20 kOhm [4607X-101-203LF]	20 kOhm [4612X-102-203LF]	20 kOhm [4816P-T01-203]
20 kOhm [4416P-2-203LF]	20 kOhm [4608H-101-203LF]	20 kOhm [4814P-1-203]	20 kOhm [4816P-T01-203LF]
20 kOhm [4416P-T01-203]	20 kOhm [4608M-102-203LF]	20 kOhm [4814P-1-203LF]	20 kOhm [4816P-T02-203]
20 kOhm [4416P-T02-203]	20 kOhm [4608X-101-203LF]	20 kOhm [4814P-2-203]	20 kOhm [4816P-T02-203LF]

Multisim 14.1 Education Components

20 kOhm [4818P-2-203]	20 kOhm [CAY16-2002F4LF]	20 kOhm [CR1206-JW-203ELF]	20 kOhm [CRT0603-FY-2002ELF]
20 kOhm [4818P-T02-203]	20 kOhm [CAY16-203J4LF]	20 kOhm [CR1206-JW-203GLF]	20 kOhm [CRT0805-BY-2002ELF]
20 kOhm [4820P-1-203]	20 kOhm [CAY16-203J8LF]	20 kOhm [CR2512-JW-203ELF]	
20 kOhm [4820P-1-203F]	20 kOhm [CAY17-203JALF]	20 kOhm [CRM1206-FX-2002ELF]	20 kOhm [CRT0805-DY-2002ELF]
20 kOhm [4820P-1-203LF]	20 kOhm [CR0201-FW-2002GLF]	20 kOhm [CRM2512-FX-2002ELF]	20 kOhm [CRT0805-DZ-2002ELF]
20 kOhm [4820P-2-203]	20 kOhm [CR0402-FX-2002GLF]	20 kOhm [CRM2512-JW-203ELF]	20 kOhm [CRT1206-BY-2002ELF]
20 kOhm [4820P-T01-203]	20 kOhm [CR0402-JW-203GLF]	20 kOhm [CRT0402-BX-2002GLF]	20 kOhm [PWR220T-20-2002J]
20 kOhm [4820P-T02-203]	20 kOhm [CR0603-FX-2002ELF]	20 kOhm [CRT0402-DZ-2002GAS]	20 kOhm [PWR220T-35-2002J]
20 kOhm [CAT10-203J4LF]	20 kOhm [CR0603-FX-2002HLF]	20 kOhm [CRT0402-FZ-2002GLF]	20 kOhm [PWR221T-30-2002F]
20 kOhm [CAT16-2002F4LF]	20 kOhm [CR0603-JW-203ELF]	20 kOhm [CRT0603-BW-2002ELF]	20 kOhm [PWR263S-35-2002F]
20 kOhm [CAT16-2002F8LF]	20 kOhm [CR0603-JW-203GLF]	20 kOhm [CRT0603-BY-2002ELF]	20 mOhm [CRA2512-FZ-R020ELF]
20 kOhm [CAT16-203J4LF]	20 kOhm [CR0805-FX-2002ELF]		
20 kOhm [CAT16-203J8LF]	20 kOhm [CR0805-JW-203ELF]		
20 kOhm [CAT25-203JALF]	20 kOhm [CR0805-JW-203GLF]		
20 kOhm [CAY10-203J4LF]	20 kOhm [CR1206-FX-2002ELF]		

Multisim 14.1 Education Components

20 mOhm [CRA2512-JZ- R020ELF]	20 mOhm [PWR1913WR020F]	20 mOhm [PWR4412- 2SBR0200F]	20 Ohm [CAT16- 200J4LF]
20 mOhm [CRF0805-FX- R020ELF]	20 mOhm [PWR1913WR020F E]	20 mOhm [PWR4412- 2SBR0200J]	20 Ohm [CAT16- 20R0F4LF]
20 mOhm [CRF1206-FZ- R020ELF]	20 mOhm [PWR1913WR020J]	20 mOhm [PWR4412- 2SCR0200F]	20 Ohm [CAY10- 200J4LF]
20 mOhm [CRF2512-FZ- R020ELF]	20 mOhm [PWR1913WR020JE]	20 mOhm [PWR4412- 2SDR0200F]	20 Ohm [CAY16- 200J8LF]
20 mOhm [CRF2512-JZ- R020ELF]	20 mOhm [PWR220T-20- R020J]	20 mOhm [PWR4525WR020J]	20 Ohm [CR0402- FX-20R0GLF]
20 mOhm [CRL1206-FU- R020ELF]	20 mOhm [PWR220T-35- R020J]	20 mOhm [PWR4525WR020JE]	20 Ohm [CR0402- JW-200GLF]
20 mOhm [CRL1206-JU- R020ELF]	20 mOhm [PWR221T-30- R020J]	20 mOhm [PWR6327WR020J]	20 Ohm [CR0603- FX-20R0ELF]
20 mOhm [CRL2010-FU- R020ELF]	20 mOhm [PWR2615WR020F]	20 mOhm [PWR6327WR020JE]	20 Ohm [CR0603- JW-200ELF]
20 mOhm [CRL2512-FU- R020ELF]	20 mOhm [PWR2615WR020F E]	20 Ohm [4114R-1- 200]	20 Ohm [CR0805- FX-20R0ELF]
20 mOhm [PWR163S-25- R020J]	20 mOhm [PWR2615WR020J]	20 Ohm [4114R-1- 200LF]	20 Ohm [CR1206- FX-20R0ELF]
20 mOhm [PWR163S-25- R020JE]	20 mOhm [PWR2615WR020JE]	20 Ohm [4310R- 101-200]	20 Ohm [CR1206- JW-200ELF]
	20 mOhm [PWR263S-35- R020J]	20 Ohm [4818P-2- 200]	20 Ohm [CR2010- FX-20R0ELF]
		20 Ohm [CAT10- 200J4LF]	20 Ohm [CR2512- FX-20R0ELF]

Multisim 14.1 Education Components

20 Ohm [CR2512-JW-200ELF]	20 Ohm [PWR220T-20-20R0F]	20 Ohm [PWR3014W20R0FE]	20 pF [C0805C200K2GACTU]
20 Ohm [CRM1206-FX-20R0ELF]	20 Ohm [PWR220T-20-20R0J]	20 Ohm [PWR3014W20R0JE]	20 pF [C0805C200K5GACTU]
20 Ohm [CRM2010-FX-20R0ELF]	20 Ohm [PWR220T-35-20R0F]	20 Ohm [PWR4318W20R0JE]	20 pF [C0805C200KBGACTU]
20 Ohm [CRM2512-FX-20R0ELF]	20 Ohm [PWR221T-30-20R0F]	20 Ohm [PWR4525W20R0F]	20 pF [C1206C200K1GACTU]
20 Ohm [CRM2512-JW-200ELF]	20 Ohm [PWR221T-30-20R0J]	20 Ohm [PWR4525W20R0J]	20 pF [C1206C200K5GACTU]
20 Ohm [CRT0805-BW-20R0ELF]	20 Ohm [PWR263S-20-20R0F]	20 Ohm [PWR5322W20R0JE]	20 pF [C1206C200KBGACTU]
20 Ohm [CRT0805-BY-20R0ELF]	20 Ohm [PWR263S-20-20R0FE]	20 pF [C0402C200K5GACTU]	20 pF [C1206C200KCGACTU]
20 Ohm [FW20A20R0JA]	20 Ohm [PWR263S-20-20R0J]	20 pF [C0402C200K8GACTU]	20 pF [C1210C200KBGACTU]
20 Ohm [PWR163S-25-20R0F]	20 Ohm [PWR263S-35-20R0F]	20 pF [C0603C200K2GACTU]	20 pF [C1812C200KBGACTU]
20 Ohm [PWR163S-25-20R0J]	20 Ohm [PWR263S-35-20R0FE]	20 pF [C0603C200K4GACTU]	20 pF [C1825C200KBGACTU]
20 Ohm [PWR163S-25-20R0JE]	20 Ohm [PWR263S-35-20R0J]	20 pF [C0603C200K5GACTU]	20 pF [C2220C200KBGACTU]
		20 pF [C0805C200K1GACTU]	

Multisim 14.1 Education Components

20 pF [C2225C200KBGAC TU]	20.5 Ohm [CRT0402-FZ- 20R5GLF]	200 kOhm [4814P- 1-204]	200 kOhm [CR0805-FX- 2003ELF]
20.5 kOhm [CR0402-FX- 2052GLF]	20_AMP 200 kOhm [4114R- 1-204]	200 kOhm [4814P- 1-204LF]	200 kOhm [CR0805-JW- 204ELF]
20.5 kOhm [CR0603-FX- 2052ELF]	200 kOhm [4114R- 1-204LF]	200 kOhm [4814P- 2-204LF]	200 kOhm [CR1206-FX- 2003ELF]
20.5 kOhm [CR0805-FX- 2052ELF]	200 kOhm [4116R- 1-204]	200 kOhm [CAT16- 2003F4LF]	200 kOhm [CR1206-JW- 204ELF]
20.5 kOhm [CR1206-FX- 2052ELF]	200 kOhm [4116R- 1-204LF]	200 kOhm [CAT16- 204J4LF]	200 kOhm [CRM2010-FX- 2003ELF]
20.5 kOhm [CRT0402-BY- 2052GLF]	200 kOhm [4306R- 102-204]	200 kOhm [CAY16- 2003F4LF]	200 kOhm [CRM2512-FX- 2003ELF]
20.5 kOhm [CRT0402-FZ- 2052GLF]	200 kOhm [4308R- 102-204]	200 kOhm [CAY16- 204J4LF]	200 kOhm [CRM2512-FX- 2003ELF]
20.5 kOhm [CRT0805-CX- 2052ELF]	200 kOhm [4308R- 102-204LF]	200 kOhm [CR0201-FW- 2003GLF]	200 kOhm [CRT0402-BY- 2003GLF]
20.5 Ohm [CR0402- FX-20R5GLF]	200 kOhm [4606X- 101-204LF]	200 kOhm [CR0402-FX- 2003GLF]	200 kOhm [CRT0603-AZ- 2003ELF]
20.5 Ohm [CR0603- FX-20R5ELF]	200 kOhm [4606X- 102-204LF]	200 kOhm [CR0402-JW- 204GLF]	200 kOhm [CRT0603-BY- 2003ELF]
20.5 Ohm [CR0805- FX-20R5ELF]	200 kOhm [4608X- 101-204LF]	200 kOhm [CR0603-FX- 2003ELF]	200 kOhm [CRT0603-FY- 2003ELF]
20.5 Ohm [CR1206- FX-20R5ELF]	200 kOhm [4610M- 102-204LF]	200 kOhm [CR0603-JW- 204ELF]	200 kOhm [CRT0805-BY- 2003ELF]

Multisim 14.1 Education Components

200 kOhm [CRT0805-DZ- 2003ELF]	200 mOhm [CRM2010-FX- R200ELF]	200 mOhm [PWR220T-35- R200F]	200 mOhm [PWR4525NR200JE]
200 mOhm [CRL0603-FW- R200ELF]	200 mOhm [CRM2512-FX- R200ELF]	200 mOhm [PWR221T-30- R200F]	200 mOhm [PWR4525WR200F]
200 mOhm [CRL0603-JW- R200ELF]	200 mOhm [CRM2512-JX- R200ELF]	200 mOhm [PWR2615NR200J]	200 mOhm [PWR4525WR200F E]
200 mOhm [CRL0805-FW- R200ELF]	200 mOhm [PWR163S-25- R200F]	200 mOhm [PWR2615NR200JE]	200 mOhm [PWR4525WR200J]
200 mOhm [CRL0805-JW- R200ELF]	200 mOhm [PWR163S-25- R200FE]	200 mOhm [PWR2615WR200J]	200 mOhm [PWR4525WR200JE]
200 mOhm [CRL1206-FW- R200ELF]	200 mOhm [PWR163S-25- R200J]	200 mOhm [PWR2615WR200JE]	200 mOhm [PWR6327NR200J]
200 mOhm [CRL1206-JW- R200ELF]	200 mOhm [PWR163S-25- R200JE]	200 mOhm [PWR263S-35- R200F]	200 mOhm [PWR6327NR200JE]
200 mOhm [CRL2010-FW- R200ELF]	200 mOhm [PWR1913WR200J]	200 mOhm [PWR263S-35- R200FE]	200 mOhm [PWR6327WR200J]
200 mOhm [CRL2010-JW- R200ELF]	200 mOhm [PWR1913WR200JE]	200 mOhm [PWR263S-35- R200JE]	200 mOhm [PWR6327WR200JE]
200 mOhm [CRL2512-FW- R200ELF]	200 mOhm [PWR220T-20- R200F]	200 mOhm [PWR3014WR200JE]	200 nH [SRP1040- R20M]
200 mOhm [CRM1206-FX- R200ELF]	200 mOhm [PWR220T-20- R200J]	200 mOhm [PWR4318WR200JE]	200 nH [SRP5015TA-R20Y]
		200 mOhm [PWR4525NR200J]	200 nH [SRP7030- R20FM]
			200 Ohm [4108R-1- 201LF]
			200 Ohm [4114R-1- 201]

Multisim 14.1 Education Components

200 Ohm [4114R-1-201LF]	200 Ohm [4606X-101-201LF]	200 Ohm [4816P-T02-201]	200 Ohm [CR0603-FX-2000GLF]
200 Ohm [4114R-2-201]	200 Ohm [4606X-102-201LF]	200 Ohm [4816P-T02-201LF]	200 Ohm [CR0603-JW-201ELF]
200 Ohm [4116R-1-201]	200 Ohm [4608X-101-201LF]	200 Ohm [CAT16-2000F4LF]	200 Ohm [CR0603-JW-201GLF]
200 Ohm [4116R-1-201LF]	200 Ohm [4608X-102-201LF]	200 Ohm [CAT16-201J4LF]	200 Ohm [CR0805-FX-2000ELF]
200 Ohm [4306R-101-201]	200 Ohm [4608X-AP2-201LF]	200 Ohm [CAT16-201J8LF]	200 Ohm [CR0805-JW-201ELF]
200 Ohm [4306R-101-201LF]	200 Ohm [4609X-101-201LF]	200 Ohm [CAT25-201JALF]	200 Ohm [CR1206-FX-2000ELF]
200 Ohm [4308R-102-201]	200 Ohm [4610X-101-201LF]	200 Ohm [CAY10-201J4LF]	200 Ohm [CR1206-JW-201ELF]
200 Ohm [4308R-102-201LF]	200 Ohm [4610X-102-201LF]	200 Ohm [CAY16-2000F4LF]	200 Ohm [CR1206-JW-201GLF]
200 Ohm [4310R-101-201]	200 Ohm [4610X-AP1-201LF]	200 Ohm [CAY16-201J4LF]	200 Ohm [CR2010-JW-201ELF]
200 Ohm [4310R-101-201LF]	200 Ohm [4816P-1-201]	200 Ohm [CAY16-201J8LF]	200 Ohm [CR2512-JW-201ELF]
200 Ohm [4310R-102-201LF]	200 Ohm [4816P-1-201LF]	200 Ohm [CR0201-FW-2000GLF]	200 Ohm [CRM1206-FX-2000ELF]
200 Ohm [4420P-1-201LF]	200 Ohm [4816P-2-201]	200 Ohm [CR0201-JW-201GLF]	200 Ohm [CRM2512-FX-2000ELF]
200 Ohm [4420P-T02-201]	200 Ohm [4816P-2-201LF]	200 Ohm [CR0402-FX-2000GLF]	200 Ohm [CRM2512-JW-201ELF]
200 Ohm [4420P-T02-201LF]	200 Ohm [4816P-T01-201]	200 Ohm [CR0402-JW-201GLF]	200 Ohm [CRM2512-JW-201ELF]
200 Ohm [4605X-101-201LF]	200 Ohm [4816P-T01-201LF]	200 Ohm [CR0603-FX-2000ELF]	200 Ohm [CRT0603-FX-2000ELF]

Multisim 14.1 Education Components

200 Ohm [CRT0805-BY- 2000ELF]	200 pF [C0402C201K1HACT U]	200 pF [C2225C201KBGAC TU]	21 kOhm [CR0603- FX-2102ELF]
200 Ohm [CRT0805-FV- 2000ELF]	200 pF [C0402C201K3HACT U]	200 uH [SDR1105- 201KL]	21 kOhm [CR0805- FX-2102ELF]
200 Ohm [PWR163S-25- 2000FE]	200 pF [C0402C201K5HACT U]	2013655-1	21 kOhm [CR1206- FX-2102ELF]
200 Ohm [PWR220T-35- 2000F]	200 pF [C0603C201K5GACT U]	205 kOhm [CR0603-FX- 2053ELF]	21 kOhm [CRT0603-BY- 2102ELF]
200 Ohm [PWR221T-30- 2000F]	200 pF [C0805C201K2GACT U]	205 kOhm [CR0805-FX- 2053ELF]	21 Ohm [CR0402- FX-21R0GLF]
200 Ohm [PWR263S-20- 2000F]	200 pF [C0805C201K5GACT U]	205 kOhm [CR1206-FX- 2053ELF]	21 Ohm [CR0603- FX-21R0ELF]
200 Ohm [PWR263S-20- 2000J]	200 pF [C1206C201K5GACT U]	205 Ohm [CR0402- FX-2050GLF]	21 Ohm [CR0805- FX-21R0ELF]
200 Ohm [PWR263S-35- 2000F]	200 pF [C1206C201KBGAC TU]	205 Ohm [CR0603- FX-2050ELF]	21 Ohm [PWR2615W21R0F]
200 Ohm [PWR263S-35- 2000FE]	200 pF [C1210C201KBGAC TU]	205 Ohm [CR0805- FX-2050ELF]	21 Ohm [PWR2615W21R0J]
200 Ohm [PWR263S-35- 2000J]	200 pF [C1812C201KBGAC TU]	205 Ohm [CR1206- FX-2050ELF]	21.5 kOhm [CAT16- 2152F4LF]
200 Ohm [PWR4525W2000F]	200 pF [C2220C201KBGAC TU]	205 Ohm [CRT0402-FZ- 2050GLF]	21.5 kOhm [CAY16- 2152F4LF]
		20CJQ030	21.5 kOhm [CR0402-FX- 2152GLF]
		20CLQ045	21.5 kOhm [CR0603-FX- 2152ELF]
		20ETS12	21.5 kOhm [CR0603-FX- 2152GLF]

Multisim 14.1 Education Components

21.5 kOhm [CR0805-FX- 2152ELF]	210 kOhm [CR0805-FX- 2103ELF]	215 Ohm [CR0402- FX-2150GLF]	22 kOhm [4306H- 102-223]
21.5 kOhm [CR1206-FX- 2152ELF]	210 kOhm [CR1206-FX- 2103ELF]	215 Ohm [CR0603- FX-2150ELF]	22 kOhm [4306H- 102-223LF]
21.5 kOhm [CRT0402-FZ- 2152GLF]	210 kOhm [CRT0805-BY- 2103ELF]	215 Ohm [CR0805- FX-2150ELF]	22 kOhm [4306M- 101-223]
21.5 kOhm [CRT0603-BY- 2152ELF]	210 Ohm [4816P-1- 211]	215 Ohm [CRT0402-FZ- 2150GLF]	22 kOhm [4306R- 101-223]
21.5 kOhm [CRT0603-FZ- 2152ELF]	210 Ohm [4816P-1- 211LF]	22 kOhm [4108R-1- 223LF]	22 kOhm [4306R- 101-223LF]
21.5 kOhm [CRT0805-DZ- 2152ELF]	210 Ohm [CR0402- FX-2100GLF]	22 kOhm [4114R-1- 223]	22 kOhm [4306R- 102-223]
21.5 Ohm [CR0603- FX-21R5ELF]	210 Ohm [CR0603- FX-2100ELF]	22 kOhm [4114R-1- 223LF]	22 kOhm [4306R- 102-223LF]
21.5 Ohm [CR0805- FX-21R5ELF]	210 Ohm [CR0805- FX-2100ELF]	22 kOhm [4114R-2- 223]	22 kOhm [4308H- 101-223]
21.5 Ohm [CR1206- FX-21R5ELF]	210 Ohm [CR1206- FX-2100ELF]	22 kOhm [4114R-2- 223LF]	22 kOhm [4308H- 102-223]
21.5 Ohm [CRT0402-FZ- 21R5GLF]	215 kOhm [CR0402-FX- 2153GLF]	22 kOhm [4116R-1- 223]	22 kOhm [4308H- 102-223LF]
210 kOhm [CR0402-FX- 2103GLF]	215 kOhm [CR0603-FX- 2153ELF]	22 kOhm [4116R-1- 223LF]	22 kOhm [4308M- 101-223]
210 kOhm [CR0603-FX- 2103ELF]	215 kOhm [CR0805-FX- 2153ELF]	22 kOhm [4116R-2- 223]	22 kOhm [4308M- 101-223LF]
		22 kOhm [4116R-2- 223LF]	22 kOhm [4308M- 102-223]
		22 kOhm [4304M- 101-223]	22 kOhm [4308M- 102-223LF]

Multisim 14.1 Education Components

22 kOhm [4308R-101-223]	22 kOhm [4416P-2-223]	22 kOhm [4606X-AP1-223LF]	22 kOhm [4610X-102-223LF]
22 kOhm [4308R-101-223LF]	22 kOhm [4416P-T02-223]	22 kOhm [4607X-101-223LF]	22 kOhm [4610X-AP1-223LF]
22 kOhm [4308R-102-223]	22 kOhm [4420P-2-223]	22 kOhm [4608H-102-223LF]	22 kOhm [4611X-101-223LF]
22 kOhm [4308R-102-223LF]	22 kOhm [4420P-2-223LF]	22 kOhm [4608X-101-223LF]	22 kOhm [4612X-102-223LF]
22 kOhm [4309R-101-223]	22 kOhm [4420P-T02-223]	22 kOhm [4608X-102-223LF]	22 kOhm [4613X-101-223LF]
22 kOhm [4309R-101-223LF]	22 kOhm [4420P-T02-223LF]	22 kOhm [4608X-AP1-223LF]	22 kOhm [4614X-102-223LF]
22 kOhm [4310H-101-223]	22 kOhm [4604X-101-223LF]	22 kOhm [4608X-AP2-223LF]	22 kOhm [4814P-1-223]
22 kOhm [4310H-101-223LF]	22 kOhm [4604X-102-223LF]	22 kOhm [4609H-101-223LF]	22 kOhm [4814P-1-223LF]
22 kOhm [4310M-101-223]	22 kOhm [4604X-AP2-223LF]	22 kOhm [4609M-101-223LF]	22 kOhm [4814P-2-223]
22 kOhm [4310R-101-223]	22 kOhm [4605X-101-223LF]	22 kOhm [4609X-101-223LF]	22 kOhm [4814P-2-223LF]
22 kOhm [4310R-101-223LF]	22 kOhm [4605X-AP1-223LF]	22 kOhm [4609X-AP1-223LF]	22 kOhm [4814P-T01-223]
22 kOhm [4310R-102-223]	22 kOhm [4606H-101-223LF]	22 kOhm [4610H-101-223LF]	22 kOhm [4814P-T01-223LF]
22 kOhm [4310R-102-223LF]	22 kOhm [4606M-101-223LF]	22 kOhm [4610H-102-223LF]	22 kOhm [4814P-T02-223]
22 kOhm [4311R-101-223LF]	22 kOhm [4606X-101-223LF]	22 kOhm [4610M-101-223LF]	22 kOhm [4814P-T02-223LF]
22 kOhm [4416P-1-223]	22 kOhm [4606X-102-223LF]	22 kOhm [4610X-101-223LF]	22 kOhm [4816P-1-223]

Multisim 14.1 Education Components

22 kOhm [4816P-1-223DLF]	22 kOhm [4820P-T02-223]	22 kOhm [CR0402-JW-223GLF]	22 kOhm [CRM2512-JW-223ELF]
22 kOhm [4816P-1-223LF]	22 kOhm [CAT10-223J4LF]	22 kOhm [CR0603-FX-2202ELF]	22 kOhm [CRT0402-BY-2202GLF]
22 kOhm [4816P-2-223]	22 kOhm [CAT16-2202F4LF]	22 kOhm [CR0603-JW-223ELF]	22 kOhm [CRT0603-PW-2202ELF]
22 kOhm [4816P-2-223LF]	22 kOhm [CAT16-223J2LF]	22 kOhm [CR0603-JW-223GLF]	22 kOhm [CRT0805-BY-2202ELF]
22 kOhm [4816P-T01-223]	22 kOhm [CAT16-223J4LF]	22 kOhm [CR0805-FX-2202ELF]	22 kOhm [CRT1206-BY-2202ELF]
22 kOhm [4816P-T01-223LF]	22 kOhm [CAT16-223J8LF]	22 kOhm [CR0805-JW-223ELF]	22 kOhm [PWR6327W2202J]
22 kOhm [4816P-T02-223]	22 kOhm [CAT25-223JALF]	22 kOhm [CR0805-JW-223GLF]	22 kOhm [PWR6327W2202JE]
22 kOhm [4816P-T02-223LF]	22 kOhm [CAY10-223J4LF]	22 kOhm [CR1206-FX-2202ELF]	22 nF [03063C223KAT2A]
22 kOhm [4818P-T02-223]	22 kOhm [CAY16-2202F4LF]	22 kOhm [CR1206-JW-223ELF]	22 nF [0306YC223KAT2A]
22 kOhm [4820P-1-223]	22 kOhm [CAY16-223J4GLF]	22 kOhm [CR1206-JW-223GLF]	22 nF [0306ZC223KAT2A]
22 kOhm [4820P-1-223LF]	22 kOhm [CAY16-223J4LF]	22 kOhm [CR2010-JW-223ELF]	22 nF [05083C223KAT2S]
22 kOhm [4820P-2-223]	22 kOhm [CAY16-223J8LF]	22 kOhm [CR2512-JW-223ELF]	22 nF [05085C223KAT2V]
22 kOhm [4820P-2-223F]	22 kOhm [CAY17-223JALF]	22 kOhm [CRM1206-FX-2202ELF]	22 nF [0508YC223KAT2S]
22 kOhm [4820P-2-223LF]	22 kOhm [CR0201-JW-223GLF]	22 kOhm [CRM1206-JW-223ELF]	
22 kOhm [4820P-T01-223]	22 kOhm [CR0402-FX-2202GLF]		

Multisim 14.1 Education Components

22 nF [06125C223KAT2W]	22 nF [C0603C223K4RACT U]	22 nF [C0805C223K5HACT U]	22 nF [C1206C223K2RACT U]
22 nF [0612ZC223KAT2S]	22 nF [C0603C223K5RACT U]	22 nF [C0805C223K5RACT U]	22 nF [C1206C223K3GACT U]
22 nF [C0402C223K3RACT U]	22 nF [C0603C223K8RACT U]	22 nF [C0805C223K8RACT U]	22 nF [C1206C223K3HACT U]
22 nF [C0402C223K4RACT U]	22 nF [C0603C223M3VAC TU]	22 nF [C0805C223KARACT U]	22 nF [C1206C223K3RACT U]
22 nF [C0402C223K5RACT U]	22 nF [C0603C223M8VAC TU]	22 nF [C0805C223M5UAC TU]	22 nF [C1206C223K4RACT U]
22 nF [C0402C223K8PACT U]	22 nF [C0805C223K1RACT U]	22 nF [C0805F223K1RACT U]	22 nF [C1206C223K5HACT U]
22 nF [C0402C223K8RACT U]	22 nF [C0805C223K2RACT U]	22 nF [C0805F223K3RACT U]	22 nF [C1206C223K5RACT U]
22 nF [C0402C223K9PACT U]	22 nF [C0805C223K3GACT U]	22 nF [C0805F223K4RACT U]	22 nF [C1206C223M5UAC TU]
22 nF [C0402C223K9RACT U]	22 nF [C0805C223K3HACT U]	22 nF [C0805F223K5RACT U]	22 nF [C1206F223K2RACT U]
22 nF [C0603C223K1RACT U]	22 nF [C0805C223K3RACT U]	22 nF [C1206C223K1HACT U]	22 nF [C1210C223K1GACT U]
22 nF [C0603C223K3RACT U]	22 nF [C0805C223K4RACT U]	22 nF [C1206C223K1RACT U]	22 nF [C1210C223K1HACT U]

Multisim 14.1 Education Components

22 nF [C1210C223K1RACT U]	22 nF [C1812C223K2RACT U]	22 nF [GMC5.7222K250J3 1TR12]	22 nF [PG124D223MAB2S 1]
22 nF [C1210C223K2RACT U]	22 nF [C1812C223K5GACT U]	22 nF [GMC5.7223K100J3 1TR12]	22 nF [PG124W223MAB2 S1]
22 nF [C1210C223K3GACT U]	22 nF [C1812C223K5HACT U]	22 nF [GMC5.7223K50J31 TR12]	22 nF [PG124Z223MAB2S 1]
22 nF [C1210C223K3HACT U]	22 nF [C1812C223K5RACT U]	22 nF [GMC7.3222K250K3 1TR12]	22 nF [PG126D223MAB2S 1]
22 nF [C1210C223K5GACT U]	22 nF [C1825C223K1GACT U]	22 nF [GMC7.3222K63K31 TR12]	22 nF [PG126W223MAB2 S1]
22 nF [C1210C223K5HACT U]	22 nF [C1825C223K5GACT U]	22 nF [GMC7.3223K63K31 TR12]	22 nF [PG126Z223MAB2S 1]
22 nF [C1210C223K5RACT U]	22 nF [C1825C223K5RACT U]	22 nF [GPC7.3223K63K31 TR12]	22 nF [PG224D223MAB2S 1]
22 nF [C1210C223KARACT U]	22 nF [C2220C223K1GACT U]	22 nF [LD16YC223KAB2A]	22 nF [PG224W223MAB2 S1]
22 nF [C1812C223K1GACT U]	22 nF [C2220C223K2GACT U]	22 nF [LG126Z223MAT2S 1]	22 nF [PG224Z223MAB2S 1]
22 nF [C1812C223K1HACT U]	22 nF [C2225C223K1GACT U]	22 nF [MMC5.7223K250J 35TR12]	22 nF [PG226D223MAB2S 1]
22 nF [C1812C223K1RACT U]	22 nF [C2225C223K5GACT U]	22 nF [MMC5.7223K50J3 1TR12]	22 nF [PG226W223MAB2 S1]

Multisim 14.1 Education Components

22 nF [PG226Z223MAB2S 1]	22 Ohm [4114R-2- 220]	22 Ohm [4308M- 102-220]	22 Ohm [4420P-1- 220LF]
22 nF [SMC5.7223K100J3 3TR12]	22 Ohm [4114R-2- 220LF]	22 Ohm [4308M- 102-220LF]	22 Ohm [4420P- T01-220]
22 nF [SPC10.2223K100A 31TR16]	22 Ohm [4116R-1- 220]	22 Ohm [4308R- 101-220]	22 Ohm [4420P- T04-220]
22 nF [SPC10.2223K250A 31TR16]	22 Ohm [4116R-1- 220LF]	22 Ohm [4308R- 101-220LF]	22 Ohm [4604X- 101-220LF]
22 nF [SPC10.2223K400A 31TR16]	22 Ohm [4116R-2- 220]	22 Ohm [4308R- 102-220]	22 Ohm [4604X- 102-220LF]
22 nF [SPC10.2223K400A 31TR16]	22 Ohm [4116R-2- 220LF]	22 Ohm [4308R- 102-220LF]	22 Ohm [4605X- 101-220LF]
22 nF [SPC12.7223K630B 31TR24]	22 Ohm [4304M- 102-220]	22 Ohm [4309R- 101-220]	22 Ohm [4606X- 101-220LF]
22 nF [SPC7.3223K100K35 TR12]	22 Ohm [4304M- 102-220LF]	22 Ohm [4310M- 102-220]	22 Ohm [4606X- 102-220LF]
22 nF [W3F15C2238AT1A]	22 Ohm [4306M- 101-220]	22 Ohm [4310R- 101-220]	22 Ohm [4606X- AP2-220LF]
22 Ohm [4108R-1- 220]	22 Ohm [4306M- 102-220]	22 Ohm [4310R- 101-220LF]	22 Ohm [4607X- 101-220LF]
22 Ohm [4108R-1- 220LF]	22 Ohm [4306R- 101-220]	22 Ohm [4310R- 102-220]	22 Ohm [4608H- 102-220LF]
22 Ohm [4114R-1- 220]	22 Ohm [4306R- 101-220LF]	22 Ohm [4310R- 102-220LF]	22 Ohm [4608X- 101-220LF]
22 Ohm [4114R-1- 220LF]	22 Ohm [4306R- 102-220LF]	22 Ohm [4416P-1- 220]	22 Ohm [4608X- 102-220LF]
	22 Ohm [4306R- 102-220LF]	22 Ohm [4416P- T01-220]	22 Ohm [4608X- AP2-220LF]
	22 Ohm [4308H- 102-220]	22 Ohm [4420P-1- 220]	22 Ohm [4609X- 101-220LF]

Multisim 14.1 Education Components

22 Ohm [4610X-101-220LF]	22 Ohm [4816P-2-220LF]	22 Ohm [CAT16-220J8LF]	22 Ohm [CR0603-FX-22R0HLF]
22 Ohm [4610X-102-220LF]	22 Ohm [4816P-T01-220]	22 Ohm [CAT16-22R0F4LF]	22 Ohm [CR0603-JW-220ELF]
22 Ohm [4610X-AP2-220LF]	22 Ohm [4816P-T01-220LF]	22 Ohm [CAT25-220JALF]	22 Ohm [CR0603-JW-220GLF]
22 Ohm [4612X-102-220LF]	22 Ohm [4816P-T02-220]	22 Ohm [CAY10-220J2LF]	22 Ohm [CR0805-FX-22R0ELF]
22 Ohm [4614X-102-220LF]	22 Ohm [4816P-T02-220LF]	22 Ohm [CAY10-220J4LF]	22 Ohm [CR0805-FX-22R0GLF]
22 Ohm [4814P-1-220]	22 Ohm [4818P-T01-220]	22 Ohm [CAY16-220J2LF]	22 Ohm [CR0805-JW-220ELF]
22 Ohm [4814P-1-220LF]	22 Ohm [4820P-1-220]	22 Ohm [CAY16-220J4LF]	22 Ohm [CR0805-JW-220GLF]
22 Ohm [4814P-2-220]	22 Ohm [4820P-1-220G]	22 Ohm [CAY16-220J8LF]	22 Ohm [CR1206-FX-22R0ELF]
22 Ohm [4814P-T01-220]	22 Ohm [4820P-1-220LF]	22 Ohm [CAY16-22R0F4LF]	22 Ohm [CR1206-FX-22R0GLF]
22 Ohm [4814P-T01-220LF]	22 Ohm [4820P-T01-220]	22 Ohm [CAY17-220JALF]	22 Ohm [CR1206-JW-220ELF]
22 Ohm [4814P-T02-220]	22 Ohm [CAT10-220J4LF]	22 Ohm [CR0201-FW-22R0GLF]	22 Ohm [CR2010-JW-220ELF]
22 Ohm [4816P-1-220]	22 Ohm [CAT16-220J2GLF]	22 Ohm [CR0201-JW-220GLF]	22 Ohm [CR2512-JW-220ELF]
22 Ohm [4816P-1-220G]	22 Ohm [CAT16-220J2LF]	22 Ohm [CR0402-FX-22R0GLF]	22 Ohm [CRM0805-JW-220ELF]
22 Ohm [4816P-1-220LF]	22 Ohm [CAT16-220J4GLF]	22 Ohm [CR0402-JW-220GLF]	22 Ohm [CRM1206-FX-22R0ELF]
22 Ohm [4816P-2-220]	22 Ohm [CAT16-220J4LF]	22 Ohm [CR0603-FX-22R0ELF]	

Multisim 14.1 Education Components

22 Ohm [CRM1206-JW-220ELF]	22 Ohm [PWR2615W22R0J]	22 pF [C0402C220K5GACTU]	22 pF [C0805C220KBGAC TU]
22 Ohm [CRM2512-JW-220ELF]	22 Ohm [PWR2615W22R0JE]]	22 pF [C0402C220K8GACTU]	22 pF [C0805C220KCGAC TU]
22 Ohm [CRT0603-FY-22R0ELF]	22 Ohm [PWR4525W22R0J]	22 pF [C0603C220K1GACTU]	22 pF [C0805C220KDGAC TU]
22 Ohm [CRT0805-BY-22R0ELF]	22 Ohm [PWR4525W22R0JE]]	22 pF [C0603C220K2GACTU]	22 pF [C1206C220K1GACTU]
22 Ohm [FW10A22R0JA]	22 Ohm [PWR6327W22R0FE]	22 pF [C0603C220K3GACTU]	22 pF [C1206C220K2GACTU]
22 Ohm [FW20A22R0JA]	22 Ohm [PWR6327W22R0J]	22 pF [C0603C220K4GACTU]	22 pF [C1206C220K5GACTU]
22 Ohm [FW30A22R0JA]	22 Ohm [PWR6327W22R0JE]]	22 pF [C0603C220K5GACTU]	22 pF [C1206C220KBGAC TU]
22 Ohm [FW50A22R0JA]	22 Ohm [W1M22R0J]	22 pF [C0805C220K1GACTU]	22 pF [C1206C220KCGAC TU]
22 Ohm [FW70A22R0JA]	22 Ohm [W3M22R0J]	22 pF [C0805C220K2GACTU]	22 pF [C1210C220K2GACTU]
22 Ohm [PWR220T-20-22R0F]	22 Ohm [WS2M22R0J]	22 pF [C0805C220K3GACTU]	22 pF [C1210C220K5GACTU]
22 Ohm [PWR220T-20-22R0J]	22 pF [C0201C220K3GACTU]	22 pF [C0805C220K5GACTU]	
22 Ohm [PWR221T-30-22R0F]	22 pF [C0402C220K3GACTU]		
22 Ohm [PWR2615W22R0F]	22 pF [C0402C220K4GACTU]		

Multisim 14.1 Education Components

22 pF [C1210C220KBGAC TU]	22 pF [W3F11A2208AT1A]	22 uF [A700V226M010AT E028]	22 uF [EEFCS1C220R]
22 pF [C1812C220KBGAC TU]	22 uF [20SVP22M] 22 uF [20TQC22MYFB]	22 uF [A700V226M12RAT E030]	22 uF [EEFCS1D220R] 22 uF [EEFCT1E220R]
22 pF [C1825C220KBGAC TU]	22 uF [25TQC22MV]	22 uF [C0805C226K9PACT U]	22 uF [EEFCX1C220R]
22 pF [C2220C220KBGAC TU]	22 uF [25TQC22MYFD]	22 uF [C1206C226K9PACT U]	22 uF [EEFCX1D220R]
22 pF [C2225C220KBGAC TU]	22 uF [25TQC22MYFT]	22 uF [C1206C226M9VAC TU]	22 uF [EEFCX1E220R]
22 pF [CA064C220K2GAC TU]	22 uF [32SEPF22M] 22 uF [35SEPF22M]	22 uF [C1210C226K4PACT U]	22 uF [EEFHX1C220R]
22 pF [CA064C220K3GAC TU]	22 uF [6TPU22MSI] 22 uF [8TPC22M]	22 uF [C1210C226K8PACT U]	22 uF [EEFHX1D220R]
22 pF [CA064C220K4GAC TU]	22 uF [A700D226M016AT E018]	22 uF [C1210C226K8PACT U]	22 uF [EEFHX1E220R]
22 pF [CA064C220K5GAC TU]	22 uF [A700V226M006AT E028]	22 uF [C1210C226K8RACT U]	22 uF [EEHZA1H220P]
22 pF [CA064C220K5GAC TU]	22 uF [A700V226M006AT E045]	22 uF [C1210C226K9PACT U]	22 uF [EEHZA1J220XP]
22 pF [CA064C220K8GAC TU]	22 uF [A700V226M008AT E028]	22 uF [C1210C226K9RACT U]	22 uF [EEHZA1K220P]
22 pF [W2F11A2208AT1A]	22 uF [A700V226M008AT E045]	22 uF [C1210C226M8VAC TU]	22 uF [EEHZC1H220P]

Multisim 14.1 Education Components

22 uF [EEHZC1J220XP]	22 uF [T491C226M016AT]	22 uF [T491U226M010AT]	22 uF [T494B226M020AT]
22 uF [EEHZC1V220R]	22 uF [T491C226M020AT]	22 uF [T491U226M016AT]	22 uF [T494C226M004AT]
22 uF [T419G226M020AH 4250]	22 uF [T491C226M025AT]	22 uF [T491V226M020AT]	22 uF [T494C226M006AT]
22 uF [T429D226M006AH 4250]	22 uF [T491D226M010AT]	22 uF [T491V226M025AT]	22 uF [T494C226M010AT]
22 uF [T491A226M004AT]	22 uF [T491D226M016AT]	22 uF [T491X226M035AT]	22 uF [T494C226M020AT]
22 uF [T491A226M006AT]	22 uF [T491D226M020AT]	22 uF [T491X226M050AT]	22 uF [T494C226M025AT]
22 uF [T491A226M010AT]	22 uF [T491D226M025AT]	22 uF [T493X226M025AH 6110]	22 uF [T494D226M010AT]
22 uF [T491B226M004AT]	22 uF [T491D226M035AT]	22 uF [T494A226M004AT]	22 uF [T494D226M016AT]
22 uF [T491B226M006AT]	22 uF [T491S226M004AT]	22 uF [T494A226M006AT]	22 uF [T494D226M020AT]
22 uF [T491B226M010AT]	22 uF [T491T226M004AT]	22 uF [T494B226M004AT]	22 uF [T494D226M025AT]
22 uF [T491B226M016AT]	22 uF [T491T226M006AT]	22 uF [T494B226M006AT]	22 uF [T494D226M035AT]
22 uF [T491B226M020AT]	22 uF [T491T226M010AT]	22 uF [T494B226M010AT]	22 uF [T494S226M004AT]
22 uF [T491C226M004AT]	22 uF [T491U226M006AT]	22 uF [T494B226M016AT]	
22 uF [T491C226M006AT]			
22 uF [T491C226M010AT]			

Multisim 14.1 Education Components

22 uF [T494T226M004AT]	22 uF [T495D226M020AT E225]	22 uF [T498C226M006AT E1K3]	22 uF [T520A226M010AT E080]
22 uF [T494T226M006AT]	22 uF [T495D226M025AT E200]	22 uF [T498C226M010AT E1K1]	22 uF [T520C226M016AT E080]
22 uF [T494T226M010AT]	22 uF [T495D226M035AT E125]	22 uF [T498C226M016AT E1K0]	22 uF [T520T226M008AT E070]
22 uF [T494U226M010AT]	22 uF [T495D226M035AT E200]	22 uF [T498D226M025AT E600]	22 uF [T520V226M020AT E045]
22 uF [T494U226M016AT]	22 uF [T495D226M035AT E300]	22 uF [T498X226M035AT E500]	22 uF [T520V226M020AT E090]
22 uF [T494V226M020AT]	22 uF [T495X226M025AT E225]	22 uF [T499D226M016AT E800]	22 uF [T521V226M025AT E060]
22 uF [T494V226M025AT]	22 uF [T495X226M035AT E125]	22 uF [T510X226M035AT E060]	22 uF [T525B226M010AT E080]
22 uF [T494X226M035AT]	22 uF [T495X226M035AT E200]	22 uF [T510X226M035AT E080]	22 uF [T541X226M050AH 6510]
22 uF [T494X226M050AT]	22 uF [T495X226M035AT E275]	22 uF [T510X226M035AT E100]	22 uF [TACR226K002RTA]
22 uF [T495C226M025AT E300]	22 uF [T497D226M006AT 6110]	22 uF [T520A226M006AT E090]	22 uF [TACR226K003RTA]
22 uF [T495C226M025AT E900]	22 uF [T498B226M010AT E1K5]	22 uF [T520A226M006AT E100]	22 uF [TACR226K004RTA]
22 uF [T495D226M020AT E180]			22 uF [TACR226K006RTA]

Multisim 14.1 Education Components

22 uF [TAJA226K004RNJ]	22 uF [TAJD226K035RNJ]	22 uF [THJB226K006RJN]	22 uF [TPSB226K006R060 0]
22 uF [TAJA226K006RNJ]	22 uF [TAJE226K035RNJ]	22 uF [THJB226K010RJN]	22 uF [TPSB226K010R040 0]
22 uF [TAJA226K010RNJ]	22 uF [TAJP226K004RNJ]	22 uF [THJC226K016RJN]	22 uF [TPSB226K010R050 0]
22 uF [TAJB226K006RNJ]	22 uF [TAJR226K004RNJ]	22 uF [THJD226K025RJN]	22 uF [TPSB226K010R070 0]
22 uF [TAJB226K010RNJ]	22 uF [TAJS226K004RNJ]	22 uF [THJD226K035R030 0]	22 uF [TPSB226K016R060 0]
22 uF [TAJB226K016RNJ]	22 uF [TAJS226K006RNJ]	22 uF [THJD226K035RJN]	22 uF [TPSC226K010R030 0]
22 uF [TAJB226K020RNJ]	22 uF [TAJT226K004RNJ]	22 uF [TPMD226K035R00 70]	22 uF [TPSC226K016R015 0]
22 uF [TAJC226K006RNJ]	22 uF [TAJT226K006RNJ]	22 uF [TPME226K035R00 60]	22 uF [TPSC226K016R025 0]
22 uF [TAJC226K010RNJ]	22 uF [TAJT226K010RNJ]	22 uF [TPME226K035R01 00]	22 uF [TPSC226K016R030 0]
22 uF [TAJC226K016RNJ]	22 uF [TAJW226K010RNJ]	22 uF [TPME226K050R01 00]	22 uF [TPSC226K016R037 5]
22 uF [TAJC226K020RNJ]	22 uF [TAJW226K016RNJ]	22 uF [TPSA226K006R050 0]	22 uF [TPSC226K020R015 0]
22 uF [TAJC226K025RNJ]	22 uF [TAJW226K020RNJ]	22 uF [TPSA226K006R090 0]	
22 uF [TAJD226K016RNJ]	22 uF [TAJY226K020RNJ]		
22 uF [TAJD226K020RNJ]	22 uF [TAJY226K025RNJ]		
22 uF [TAJD226K025RNJ]	22 uF [TAJY226K035RNJ]		

Multisim 14.1 Education Components

22 uF [TPSC226K020R040 0]	22 uF [TPSE226K035R012 5]	22 uF [TRME226K035R01 00]	22 uH [SDR1030- 220M]
22 uF [TPSC226K025R040 0]	22 uF [TPSE226K035R020 0]	22 uH [SDE0403A- 220M]	22 uH [SDR1045- 220M]
22 uF [TPSD226K020R020 0]	22 uF [TPSE226K035R030 0]	22 uH [SDE0604A- 220M]	22 uH [SDR1105- 220ML]
22 uF [TPSD226K020R030 0]	22 uF [TPST226K010R080 0]	22 uH [SDE0805A- 220M]	22 uH [SDR1305- 220M]
22 uF [TPSD226K025R010 0]	22 uF [TPSW226K016R05 00]	22 uH [SDE1006A- 220M]	22 uH [SDR1307- 220ML]
22 uF [TPSD226K025R020 0]	22 uF [TRJA226K006RRJ]	22 uH [SDR0302- 220ML]	22 uH [SDR1307A- 220M]
22 uF [TPSD226K025R030 0]	22 uF [TRJB226K006RRJ]	22 uH [SDR0403- 220ML]	22 uH [SDR1806- 220ML]
22 uF [TPSD226K035R012 5]	22 uF [TRJB226K010RRJ]	22 uH [SDR0503- 220ML]	22 uH [SDR6603- 220M]
22 uF [TPSD226K035R020 0]	22 uF [TRJC226K016RRJ]	22 uH [SDR0603- 220ML]	22 uH [SDR7030- 220M]
22 uF [TPSD226K035R030 0]	22 uF [TRJD226K035RRJ]	22 uH [SDR0604- 220YL]	22 uH [SDR7045- 220M]
22 uF [TPSD226K035R040 0]	22 uF [TRME226K035R00 60]	22 uH [SDR0703- 220KL]	22 uH [SRN1060- 220M]
		22 uH [SDR0805- 220ML]	22 uH [SRN3010- 220M]
		22 uH [SDR0906- 220ML]	22 uH [SRN3015- 220M]
		22 uH [SDR1005- 220ML]	22 uH [SRN4012T- 220M]
		22 uH [SDR1006- 220ML]	22 uH [SRN4018- 220M]

Multisim 14.1 Education Components

22 uH [SRN4026-220M]	22 uH [SRR0735A-220M]	22 uH [SRR1260-220M]	22 uH [SRR7045-220M]
22 uH [SRN5020-220M]	22 uH [SRR0745A-220M]	22 uH [SRR1260A-220M]	22 uH [SRU1028-220Y]
22 uH [SRN5040-220M]	22 uH [SRR0804-220Y]	22 uH [SRR1280-220M]	22 uH [SRU1028A-220Y]
22 uH [SRN6028-220M]	22 uH [SRR0805-220Y]	22 uH [SRR1806-220M]	22 uH [SRU1038-220Y]
22 uH [SRN6045-220M]	22 uH [SRR0905-220M]	22 uH [SRR3011-220YL]	22 uH [SRU1038A-220Y]
22 uH [SRN8040-220M]	22 uH [SRR0906-220ML]	22 uH [SRR4011-220YL]	22 uH [SRU1048-220Y]
22 uH [SRP1038A-220M]	22 uH [SRR0908-220ML]	22 uH [SRR4018-220Y]	22 uH [SRU1048A-220Y]
22 uH [SRP1265A-220M]	22 uH [SRR1003-220M]	22 uH [SRR4028-220Y]	22 uH [SRU1063-220Y]
22 uH [SRP1770TA-220M]	22 uH [SRR1005-220Y]	22 uH [SRR5018-220Y]	22 uH [SRU2009-220Y]
22 uH [SRP5015TA-220M]	22 uH [SRR1205-220ML]	22 uH [SRR5028-220Y]	22 uH [SRU2011-220Y]
22 uH [SRP6540-220M]	22 uH [SRR1206-220ML]	22 uH [SRR6028-220Y]	22 uH [SRU2013-220Y]
22 uH [SRP7050TA-220M]	22 uH [SRR1208-220ML]	22 uH [SRR6038-220Y]	22 uH [SRU2016-220Y]
22 uH [SRR0603-220ML]	22 uH [SRR1210-220M]	22 uH [SRR6040A-220M]	22 uH [SRU3014-220Y]
22 uH [SRR0604-220ML]	22 uH [SRR1210A-220M]	22 uH [SRR6603-220ML]	22 uH [SRU3017-220Y]
22 uH [SRR0618-220ML]	22 uH [SRR1240-220M]	22 uH [SRR7032-220M]	22 uH [SRU3028-220Y]

Multisim 14.1 Education Components

22 uH [SRU3028A-220Y]	22.1 kOhm [CR0402-FX-2212GLF]	22.1 Ohm [CR0805-FX-22R1ELF]	22.6 kOhm [CRT1206-FZ-2262ELF]
22 uH [SRU5011-220Y]	22.1 kOhm [CR0603-FX-2212ELF]	22.1 Ohm [CR1206-FX-22R1ELF]	22.6 Ohm [CR0402-FX-22R6GLF]
22 uH [SRU5016-220Y]	22.1 kOhm [CR0805-FX-2212ELF]	22.1 Ohm [CR2010-FX-22R1ELF]	22.6 Ohm [CR0603-FX-22R6ELF]
22 uH [SRU5018-220Y]	22.1 kOhm [CR1206-FX-2212ELF]	22.1 Ohm [CR2512-FX-22R1ELF]	22.6 Ohm [CR0805-FX-22R6ELF]
22 uH [SRU5028-220Y]	22.1 kOhm [CR1206-FX-2212ELF]	22.1 Ohm [CRM1206-FX-22R1ELF]	22.6 Ohm [CR1206-FX-22R6ELF]
22 uH [SRU5028A-220Y]	22.1 kOhm [CR1206-FX-2212GLF]	22.1 Ohm [CRT0805-DW-22R1ELF]	22.6 Ohm [CRT0402-FZ-22R6GLF]
22 uH [SRU6011-220Y]	22.1 kOhm [CRT0603-BY-2212ELF]	22.6 kOhm [CR0402-FX-2262GLF]	220 kOhm [4114R-1-224]
22 uH [SRU6018-220Y]	22.1 kOhm [CRT0805-BY-2212ELF]	22.6 kOhm [CR0603-FX-2262ELF]	220 kOhm [4114R-1-224LF]
22 uH [SRU6025-220Y]	22.1 Ohm [CAT16-22R1F4LF]	22.6 kOhm [CR0805-FX-2262ELF]	220 kOhm [4114R-2-224]
22 uH [SRU6025A-220Y]	22.1 Ohm [CAT16-22R1F8LF]	22.6 kOhm [CR1206-FX-2262ELF]	220 kOhm [4114R-2-224LF]
22 uH [SRU8028-220Y]	22.1 Ohm [CAY16-22R1F4LF]	22.6 kOhm [CRT0402-BY-2262GLF]	220 kOhm [4116R-1-224]
22 uH [SRU8028A-220Y]	22.1 Ohm [CR0402-FX-22R1GLF]	22.6 kOhm [CRT0805-BY-2262ELF]	220 kOhm [4116R-1-224LF]
22 uH [SRU8043-220Y]	22.1 Ohm [CR0603-FX-22R1ELF]	22.6 kOhm [4304M-101-224]	
22.1 kOhm [CAT16-2212F4LF]	22.1 Ohm [CR0603-FX-22R1GLF]		
22.1 kOhm [CAY16-2212F4LF]			

Multisim 14.1 Education Components

220 kOhm [4306R-101-224]	220 kOhm [4310R-101-224]	220 kOhm [4608X-AP1-224LF]	220 kOhm [4816P-2-224LF]
220 kOhm [4306R-101-224LF]	220 kOhm [4310R-101-224LF]	220 kOhm [4608X-AP2-224LF]	220 kOhm [4816P-T01-224]
220 kOhm [4306R-102-224]	220 kOhm [4310R-102-224]	220 kOhm [4609X-101-224LF]	220 kOhm [4816P-T01-224LF]
220 kOhm [4306R-102-224LF]	220 kOhm [4310R-102-224LF]	220 kOhm [4609X-AP1-224LF]	220 kOhm [4816P-T02-224]
220 kOhm [4308H-101-224LF]	220 kOhm [4416P-1-224]	220 kOhm [4610X-101-224LF]	220 kOhm [4816P-T02-224LF]
220 kOhm [4308M-101-224]	220 kOhm [4604X-101-224LF]	220 kOhm [4610X-102-224LF]	220 kOhm [4820P-1-224]
220 kOhm [4308M-102-224]	220 kOhm [4604X-102-224LF]	220 kOhm [4610X-AP1-224LF]	220 kOhm [4820P-2-224]
220 kOhm [4308M-102-224LF]	220 kOhm [4604X-AP2-224LF]	220 kOhm [4611X-101-224LF]	220 kOhm [4820P-2-224LF]
220 kOhm [4308R-101-224]	220 kOhm [4605X-101-224LF]	220 kOhm [4612X-102-224LF]	220 kOhm [CAT16-2203F4LF]
220 kOhm [4308R-101-224LF]	220 kOhm [4606H-101-224LF]	220 kOhm [4814P-1-224]	220 kOhm [CAT16-224J4LF]
220 kOhm [4308R-102-224]	220 kOhm [4606X-101-224LF]	220 kOhm [4814P-1-224LF]	220 kOhm [CAT16-224J8LF]
220 kOhm [4308R-102-224LF]	220 kOhm [4606X-102-224LF]	220 kOhm [4816P-1-224]	220 kOhm [CAT25-224JALF]
220 kOhm [4309R-101-224]	220 kOhm [4606X-AP1-224LF]	220 kOhm [4816P-1-224F]	220 kOhm [CAY10-224J4LF]
220 kOhm [4310H-101-224]	220 kOhm [4608X-101-224LF]	220 kOhm [4816P-1-224LF]	220 kOhm [CAY16-2203F4LF]
220 kOhm [4310H-101-224LF]	220 kOhm [4608X-102-224LF]	220 kOhm [4816P-2-224]	220 kOhm [CAY16-224J4LF]

Multisim 14.1 Education Components

220 kOhm [CAY16-224J8LF]	220 kOhm [CR0805-JW-224ELF]	220 mOhm [CRL0805-FW-R220ELF]	220 mOhm [PWR4318WR220JE]
220 kOhm [CHV0603-FX-2203ELF]	220 kOhm [CR1206-FX-2203ELF]	220 mOhm [CRL0805-JW-R220ELF]	220 mOhm [PWR4525NR220F]
220 kOhm [CHV0805-FX-2203ELF]	220 kOhm [CR1206-JW-224ELF]	220 mOhm [CRL1206-FW-R220ELF]	220 mOhm [PWR4525WR220FE]
220 kOhm [CHV1206-JW-224ELF]	220 kOhm [CRM1206-FX-2203ELF]	220 mOhm [CRL1206-JW-R220ELF]	220 nF [03066C224KAT2A]
220 kOhm [CHV2010-FX-2203ELF]	220 kOhm [CRM2512-FX-2203ELF]	220 mOhm [CRL2010-FW-R220ELF]	220 nF [0306ZC224KAT2A]
220 kOhm [CHV2512-FX-2203ELF]	220 kOhm [CRM2512-JW-224ELF]	220 mOhm [CRL2010-JW-R220ELF]	220 nF [0508YC224KAT2A]
220 kOhm [CR0402-FX-2203GLF]	220 kOhm [CRT1206-BX-2203ELF]	220 mOhm [CRL2512-FW-R220ELF]	220 nF [0508ZC224KAT2S]
220 kOhm [CR0402-JW-224GLF]	220 kOhm [CRT1206-DX-2203ELF]	220 mOhm [CRL2512-JW-R220ELF]	220 nF [06123C224KAT2W]
220 kOhm [CR0603-FX-2203ELF]	220 kOhm [CRT1206-DY-2203ELF]	220 mOhm [CRM1206-FX-R220ELF]	220 nF [0612YC224KAT2V]
220 kOhm [CR0603-JW-224ELF]	220 mOhm [CRL0603-FW-R220ELF]	220 mOhm [CRM2010-FX-R220ELF]	220 nF [C0402C224K9PACTU]
220 kOhm [CR0805-FX-2203ELF]	220 mOhm [CRL0603-JW-R220ELF]	220 mOhm [CRM2512-FX-R220ELF]	220 nF [C0603C224K3RACTU]
			220 nF [C0603C224K4RACTU]
			220 nF [C0603C224K8NACTU]

Multisim 14.1 Education Components

220 nF [C0603C224K8RACT U]	220 nF [C1206C224K1RACT U]	220 nF [C1210C224K5RACT U]	220 nF [C1812F224K1RACT U]
220 nF [C0603C224K9RACT U]	220 nF [C1206C224K3RACT U]	220 nF [C1210C224M5UAC TU]	220 nF [C1812F224K2RACT U]
220 nF [C0603C224M3VAC TU]	220 nF [C1206C224K4RACT U]	220 nF [C1210F224K1RACT U]	220 nF [C1812F224K3RACT U]
220 nF [C0603C224M4VAC TU]	220 nF [C1206C224K5RACT U]	220 nF [C1210F224K3RACT U]	220 nF [C1812F224K5RACT U]
220 nF [C0603C224M8VAC TU]	220 nF [C1206C224M5UAC TU]	220 nF [C1210F224K4RACT U]	220 nF [C1825C224K1RACT U]
220 nF [C0805C224K3RACT U]	220 nF [C1206F224K3RACT U]	220 nF [C1210F224K5RACT U]	220 nF [C1825C224K2RACT U]
220 nF [C0805C224K4RACT U]	220 nF [C1206F224K4RACT U]	220 nF [C1812C224K1RACT U]	220 nF [C1825C224K5RACT U]
220 nF [C0805C224K5RACT U]	220 nF [C1206F224K5RACT U]	220 nF [C1812C224K5HACT U]	220 nF [C1825C224M1UAC TU]
220 nF [C0805C224K8RACT U]	220 nF [C1210C224K1RACT U]	220 nF [C1812C224K5RACT U]	220 nF [C1825C224M5UAC TU]
220 nF [C0805C224M3VAC TU]	220 nF [C1210C224K3GACT U]	220 nF [C1812C224KARACT U]	220 nF [C2220C224K1GACT U]
220 nF [C0805C224M4VAC TU]	220 nF [C1210C224K3RACT U]	220 nF [C1812C224M5UAC TU]	220 nF [C2220C224K5GACT U]

Multisim 14.1 Education Components

220 nF [C2225C224K1RACT U]	220 nF [MDC10224K50A52 P3TUBE]	220 nF [MDS15224K100B5 3P3TUBE]	220 nF [T494A224M035AT]
220 nF [C2225C224K5RACT U]	220 nF [MDC15224K100B5 3P3TUBE]	220 nF [MDS15224K250B5 3P3TUBE]	220 nF [T494B224M050AT]
220 nF [GMC7.3224K63K33 TR12]	220 nF [MDC15224K250B5 3P3TUBE]	220 nF [PG224D224MAB2S 1]	220 nF [T499A224M035AT E18K]
220 nF [LD166C224KAB2A]	220 nF [MDC15224K400B5 3P3TUBE]	220 nF [PG224W224MAB2 S1]	220 nF [TAJA224K035RNJ]
220 nF [LD16ZC224KAB2A]	220 nF [MDC15224K50B53 P3TUBE]	220 nF [PG224Z224MAB2S 1]	220 nF [TAJB224K050RNJ]
220 nF [LD17ZC224KAB2S]	220 nF [MDK10224K100A5 2P3TUBE]	220 nF [PG226D224MAB2S 1]	220 nF [TAJR224K020RNJ]
220 nF [LG224Z224MAT2S 1]	220 nF [MDK10224K250A5 2P3TUBE]	220 nF [SPC12.7224K100B 31TR24]	220 nF [TAJS224K020RNJ]
220 nF [LG226D224MAT2S 1]	220 nF [MDK10224K50A52 P3TUBE]	220 nF [SPC16.5224K250C 31TR24]	220 nF [TAJS224K035RNJ]
220 nF [MDC10224K100A5 2P3TUBE]	220 nF [MDS10224K100A5 2P3TUBE]	220 nF [T409A224M035AH 4250]	220 nF [THJA224K035RJN]
220 nF [MDC10224K250A5 2P3TUBE]	220 nF [MDS10224K250A5 2P3TUBE]	220 nF [T491A224M035AT]	220 nF [TPSA224K035R600 0]
220 nF [MDC10224K400A5 7P7TUBE]	220 nF [MDS10224K50A52 P3TUBE]	220 nF [T491B224M050AT]	220 nF [TPSA224K050R700 0]
220 nF [MDC10224K400A5 7P8TUBE]		220 nF [T493B224M050AH 6120]	220 nF [W2L1YC224MAT1A]

Multisim 14.1 Education Components

220 nF [W2L1ZC224MAT1S]	220 Ohm [4114R-1- 221]	220 Ohm [4306R- 101-221]	220 Ohm [4309R- 101-221]
220 nF [W3L1YC224MAT1A]	220 Ohm [4114R-1- 221LF]	220 Ohm [4306R- 101-221LF]	220 Ohm [4309R- 101-221LF]
220 nF [W3L1YC224MAT1S]	220 Ohm [4114R-2- 221]	220 Ohm [4306R- 102-221]	220 Ohm [4310H- 101-221]
220 nH [SRP1038A- R22M]	220 Ohm [4114R-2- 221LF]	220 Ohm [4306R- 102-221LF]	220 Ohm [4310H- 101-221LF]
220 nH [SRP1235- R22M]	220 Ohm [4116R-1- 221]	220 Ohm [4308H- 101-221]	220 Ohm [4310H- 102-221]
220 nH [SRP1235- R22M]	220 Ohm [4116R-1- 221LF]	220 Ohm [4308H- 101-221LF]	220 Ohm [4310M- 101-221]
220 nH [SRP1250- R22M]	220 Ohm [4116R-2- 221]	220 Ohm [4308H- 102-221]	220 Ohm [4310R- 101-221]
220 nH [SRP4012- R22M]	220 Ohm [4116R-2- 221LF]	220 Ohm [4308M- 101-221]	220 Ohm [4310R- 101-221LF]
220 nH [SRP4012TA-R22M]	220 Ohm [4304M- 101-221]	220 Ohm [4308M- 101-221LF]	220 Ohm [4310R- 102-221]
220 nH [SRP4020- R22M]	220 Ohm [4304M- 101-221LF]	220 Ohm [4308M- 102-221]	220 Ohm [4310R- 102-221LF]
220 nH [SRP4020TA-R22Y]	220 Ohm [4304M- 102-221]	220 Ohm [4308M- 102-221LF]	220 Ohm [4416P-1- 221]
220 nH [SRP5015TA-R22Y]	220 Ohm [4304M- 102-221LF]	220 Ohm [4308R- 101-221]	220 Ohm [4416P-1- 221LF]
220 nH [SRP7028A- R22Y]	220 Ohm [4306H- 101-221]	220 Ohm [4308R- 101-221LF]	220 Ohm [4416P-2- 221]
220 nH [SRP7030- R22FM]	220 Ohm [4306M- 101-221]	220 Ohm [4308R- 102-221]	220 Ohm [4416P- T01-221]
220 nH [SRP8040- R22Y]	220 Ohm [4306M- 101-221LF]	220 Ohm [4308R- 102-221LF]	220 Ohm [4416P- T02-221]

Multisim 14.1 Education Components

220 Ohm [4420P-1-221]	220 Ohm [4608X-101-221LF]	220 Ohm [4814P-1-221]	220 Ohm [4816P-T02-221]
220 Ohm [4420P-1-221LF]	220 Ohm [4608X-102-221LF]	220 Ohm [4814P-1-221LF]	220 Ohm [4816P-T02-221LF]
220 Ohm [4420P-2-221]	220 Ohm [4608X-AP2-221LF]	220 Ohm [4814P-2-221]	220 Ohm [4820P-1-221]
220 Ohm [4420P-T01-221]	220 Ohm [4609H-101-221LF]	220 Ohm [4814P-2-221LF]	220 Ohm [4820P-1-221LF]
220 Ohm [4420P-T02-221]	220 Ohm [4609M-101-221LF]	220 Ohm [4814P-T01-221]	220 Ohm [4820P-2-221]
220 Ohm [4420P-T02-221LF]	220 Ohm [4609X-101-221LF]	220 Ohm [4814P-T01-221LF]	220 Ohm [4820P-T01-221]
220 Ohm [4604X-101-221LF]	220 Ohm [4609X-AP1-221LF]	220 Ohm [4814P-T02-221]	220 Ohm [4820P-T02-221]
220 Ohm [4604X-102-221LF]	220 Ohm [4610H-101-221LF]	220 Ohm [4814P-T02-221LF]	220 Ohm [CAT10-221J4LF]
220 Ohm [4605X-101-221LF]	220 Ohm [4610X-101-221LF]	220 Ohm [4816P-1-221]	220 Ohm [CAT16-2200F4LF]
220 Ohm [4606X-101-221LF]	220 Ohm [4610X-102-221LF]	220 Ohm [4816P-1-221LF]	220 Ohm [CAT16-221J2LF]
220 Ohm [4606X-102-221LF]	220 Ohm [4611X-101-221LF]	220 Ohm [4816P-2-221]	220 Ohm [CAT16-221J4LF]
220 Ohm [4606X-AP2-221LF]	220 Ohm [4612X-102-221LF]	220 Ohm [4816P-2-221F]	220 Ohm [CAT16-221J8LF]
220 Ohm [4607X-101-221LF]	220 Ohm [4613X-101-221LF]	220 Ohm [4816P-2-221LF]	220 Ohm [CAT25-221JALF]
220 Ohm [4608H-101-221LF]	220 Ohm [4614X-101-221LF]	220 Ohm [4816P-T01-221]	220 Ohm [CAY10-221J4LF]
220 Ohm [4608H-102-221LF]	220 Ohm [4614X-102-221LF]	220 Ohm [4816P-T01-221LF]	220 Ohm [CAY16-2200F4LF]

Multisim 14.1 Education Components

220 Ohm [CAY16-221J4GLF]	220 Ohm [CR1206-JW-221ELF]	220 Ohm [PWR6327W2200JE]	220 pF [C0603C221K3GACTU]
220 Ohm [CAY16-221J4LF]	220 Ohm [CR2010-JW-221ELF]	220 pF [C0402C221K1HACTU]	220 pF [C0603C221K3RACTU]
220 Ohm [CAY16-221J8LF]	220 Ohm [CR2512-JW-221ELF]	220 pF [C0402C221K3HACTU]	220 pF [C0603C221K4GACTU]
220 Ohm [CAY17-221JALF]	220 Ohm [CRM1206-FX-2200ELF]	220 pF [C0402C221K3RACTU]	220 pF [C0603C221K4RACTU]
220 Ohm [CR0201-FW-2200GLF]	220 Ohm [CRM2512-FX-2200ELF]	220 pF [C0402C221K4RACTU]	220 pF [C0603C221K5GACTU]
220 Ohm [CR0402-FX-2200GLF]	220 Ohm [CRM2512-JW-221ELF]	220 pF [C0402C221K5GACTU]	220 pF [C0603C221K5RACTU]
220 Ohm [CR0402-JW-221GLF]	220 Ohm [PWR2615W2200J]	220 pF [C0402C221K5HACTU]	220 pF [C0603C221K8RACTU]
220 Ohm [CR0603-FX-2200ELF]	220 Ohm [PWR2615W2200JE]	220 pF [C0402C221K5RACTU]	220 pF [C0805C221K1GACTU]
220 Ohm [CR0603-JW-221ELF]	220 Ohm [PWR263S-35-2200FE]	220 pF [C0402C221K8RACTU]	220 pF [C0805C221K1RACTU]
220 Ohm [CR0603-JW-221GLF]	220 Ohm [PWR263S-35-2200J]	220 pF [C0603C221K1RACTU]	220 pF [C0805C221K2GACTU]
220 Ohm [CR0805-FX-2200ELF]	220 Ohm [PWR4525W2200J]	220 pF [C0603C221K2RACTU]	
220 Ohm [CR0805-FX-2200GLF]	220 Ohm [PWR4525W2200JE]		
220 Ohm [CR0805-JW-221ELF]			
220 Ohm [CR0805-JW-221GLF]			
220 Ohm [CR1206-FX-2200ELF]			
	220 Ohm [PWR6327W2200J]		

Multisim 14.1 Education Components

220 pF [C0805C221K3GACT U]	220 pF [C1206C221KCGAC TU]	220 pF [W3F11A2218AT1A]	220 uF [2R5TPE220MZB]
220 pF [C0805C221K3RACT U]	220 pF [C1206C221KDGAC TU]	220 uF [10TPB220M]	220 uF [2R5TPG220M]
220 pF [C0805C221K4RACT U]	220 pF [C1210C221K1GACT U]	220 uF [10TPB220ML]	220 uF [2R5TPG220MUG]
220 pF [C0805C221K5GACT U]	220 pF [C1210C221KBGAC TU]	220 uF [10TPE220MIL]	220 uF [4TPE220M]
220 pF [C0805C221K5RACT U]	220 pF [C1812C221KBGAC TU]	220 uF [16SEPC220MD]	220 uF [4TPE220MF]
220 pF [C0805C221K8RACT U]	220 pF [C1825C221KBGAC TU]	220 uF [2R5TPE220M]	220 uF [4TPE220MI]
220 pF [C0805C221KARACT U]	220 pF [C2220C221KBGAC TU]	220 uF [2R5TPE220MAFB]	220 uF [4TPG220M]
220 pF [C1206C221K1GACT U]	220 pF [C2225C221KBGAC TU]	220 uF [2R5TPE220MAPB]	220 uF [6SVPC220MV]
220 pF [C1206C221K2GACT U]	220 pF [CA064C221K5GAC TU]	220 uF [2R5TPE220MAZB]	220 uF [6SVPE220M]
220 pF [C1206C221K5GACT U]	220 pF [CDR02BP221BKSM]	220 uF [2R5TPE220MF]	220 uF [6SVPE220MW]
220 pF [C1206C221KBGAC TU]	220 pF [W2F11A2218AT1A]	220 uF [2R5TPE220MFGB]	220 uF [6TPB220ML]
		220 uF [2R5TPE220MI]	220 uF [6TPE220M]
		220 uF [2R5TPE220MLB]	220 uF [6TPE220MAP]

Multisim 14.1 Education Components

220 uF [6TPE220MAZB]	220 uF [A700X227M2R5AT E015]	220 uF [EEFSX0G221ER]	220 uF [T491X227M010AT]
220 uF [6TPE220MI]	220 uF [EEFCX0D221R]	220 uF [EEHZA1E221P]	220 uF [T491X227M016AT]
220 uF [6TPPF220M5L]	220 uF [EEFCX0E221R]	220 uF [EEHZC1E221P]	220 uF [T494B227M004AT]
220 uF [6TPPF220M9L]	220 uF [EEFCX0G221R]	220 uF [ETPH220MABC]	220 uF [T494C227M006AT]
220 uF [6TPPF220ML]	220 uF [EEFCX0G221XR]	220 uF [T419H227M004AH 4250]	220 uF [T494D227M006AT]
220 uF [A700D227M002AT E015]	220 uF [EEFCX0J221R]	220 uF [T491B227M004AT]	220 uF [T494D227M010AT]
220 uF [A700D227M002AT E018]	220 uF [EEFLR0D221R]	220 uF [T491C227M006AT]	220 uF [T494D227M2R5AT]
220 uF [A700D227M004AT E009]	220 uF [EEFLR0D221R4]	220 uF [T491D227M006AT]	220 uF [T494E227M016AT]
220 uF [A700V227M002AT E009]	220 uF [EEFLS0D221R]	220 uF [T491D227M010AT]	220 uF [T494V227M004AT]
220 uF [A700X227M004AT E010]	220 uF [EEFSR0D221R4]	220 uF [T491D227M2R5AT]	220 uF [T494V227M006AT]
220 uF [A700X227M004AT E015]	220 uF [EEFSS0D221R]	220 uF [T491E227M016AT]	220 uF [T494X227M006AT]
220 uF [A700X227M2R5AT E010]	220 uF [EEFSX0D221ER]	220 uF [T491V227M004AT]	220 uF [T494X227M010AT]
	220 uF [EEFSX0E221E7]	220 uF [T491V227M006AT]	220 uF [T494X227M016AT]
	220 uF [EEFSX0E221ER]	220 uF [T491X227M006AT]	220 uF [T495C227M006AT E225]

Multisim 14.1 Education Components

220 uF [T495D227M004AT E040]	220 uF [T495E227M016AT E075]	220 uF [T510X227M016AT E025]	220 uF [T520B227M2R5AT E030]
220 uF [T495D227M004AT E050]	220 uF [T495E227M016AT E150]	220 uF [T510X227M016AT E040]	220 uF [T520B227M2R5AT E035]
220 uF [T495D227M004AT E100]	220 uF [T495X227M006AT E100]	220 uF [T513X227M016AH 6110]	220 uF [T520B227M2R5AT E070]
220 uF [T495D227M006AT E045]	220 uF [T495X227M010AT E045]	220 uF [T513X227M016AH 6120]	220 uF [T520C227M004AT E018]
220 uF [T495D227M006AT E100]	220 uF [T495X227M010AT E050]	220 uF [T520B227M004AT E035]	220 uF [T520C227M004AT E025]
220 uF [T495D227M010AT E045]	220 uF [T495X227M010AT E060]	220 uF [T520B227M004AT E045]	220 uF [T520C227M004AT E045]
220 uF [T495D227M010AT E075]	220 uF [T495X227M010AT E070]	220 uF [T520B227M004AT E070]	220 uF [T520C227M004AT E055]
220 uF [T495D227M010AT E100]	220 uF [T495X227M010AT E100]	220 uF [T520B227M006AT E035]	220 uF [T520C227M006AT E025]
220 uF [T495D227M010AT E125]	220 uF [T495X227M016AT E100]	220 uF [T520B227M2R5AT E015]	220 uF [T520C227M006AT E045]
220 uF [T495D227M2R5AT E045]	220 uF [T496X227M010AT 6110]	220 uF [T520B227M2R5AT E018]	220 uF [T520C227M2R5AT E025]
220 uF [T495E227M016AT E050]	220 uF [T498X227M010AT E500]	220 uF [T520B227M2R5AT E025]	220 uF [T520D227M004AT E012]

Multisim 14.1 Education Components

220 uF [T520D227M004AT E065]	220 uF [T520D227M2R5AT E040]	220 uF [T520V227M006AT E007]	220 uF [T520V227M2R5AT E015]
220 uF [T520D227M006AT E006]	220 uF [T520U227M2R5AT E055]	220 uF [T520V227M006AT E009]	220 uF [T520V227M2R5AT E025]
220 uF [T520D227M006AT E007]	220 uF [T520V227M004AT E006]	220 uF [T520V227M006AT E012]	220 uF [T520V227M2R5AT E045]
220 uF [T520D227M006AT E009]	220 uF [T520V227M004AT E007]	220 uF [T520V227M006AT E015]	220 uF [T520W227M004AT E025]
220 uF [T520D227M006AT E015]	220 uF [T520V227M004AT E009]	220 uF [T520V227M006AT E018]	220 uF [T520W227M004AT E040]
220 uF [T520D227M006AT E040]	220 uF [T520V227M004AT E012]	220 uF [T520V227M006AT E025]	220 uF [T520Y227M010AT E040]
220 uF [T520D227M006AT E050]	220 uF [T520V227M004AT E015]	220 uF [T520V227M006AT E040]	220 uF [T522V227M006AT E025]
220 uF [T520D227M010AT E018]	220 uF [T520V227M004AT E018]	220 uF [T520V227M010AT E045]	220 uF [T522V227M006AT E040]
220 uF [T520D227M010AT E025]	220 uF [T520V227M004AT E025]	220 uF [T520V227M2R5AT E007]	220 uF [T525D227M004AT E025]
220 uF [T520D227M010AT E040]	220 uF [T520V227M004AT E040]	220 uF [T520V227M2R5AT E009]	220 uF [T525D227M006AT E025]
220 uF [T520D227M2R5AT E007]	220 uF [T520V227M004AT E045]	220 uF [T520V227M2R5AT E012]	220 uF [T525D227M010AT E025]

Multisim 14.1 Education Components

220 uF [T528Z227M004AT E007]	220 uF [T543V227M004AT E015]	220 uF [TAJY227K010RNJ]	220 uF [TPSD227K006R005 0]
220 uF [T528Z227M004AT E009]	220 uF [TAJB227K002RNJ]	220 uF [THJE227K010RJN]	220 uF [TPSD227K006R010 0]
220 uF [T528Z227M004AT E012]	220 uF [TAJC227K004RNJ]	220 uF [TPME227K016R00 25]	220 uF [TPSD227K006R012 5]
220 uF [T528Z227M006AT E009]	220 uF [TAJC227K006RNJ]	220 uF [TPME227K016R00 40]	220 uF [TPSD227K010R005 0]
220 uF [T528Z227M006AT E012]	220 uF [TAJD227K004RNJ]	220 uF [TPSB227K002R060 0]	220 uF [TPSD227K010R010 0]
220 uF [T530D227M006AT E005]	220 uF [TAJD227K006RNJ]	220 uF [TPSC227K006R007 0]	220 uF [TPSD227K010R015 0]
220 uF [T530D227M006AT E006]	220 uF [TAJE227K006RNJ]	220 uF [TPSC227K006R010 0]	220 uF [TPSE227K006R010 0]
220 uF [T530D227M010AT E006]	220 uF [TAJE227K010RNJ]	220 uF [TPSC227K006R012 5]	220 uF [TPSE227K010R005 0]
220 uF [T530D227M010AT E010]	220 uF [TAJE227K016RNJ]	220 uF [TPSC227K006R025 0]	220 uF [TPSE227K010R006 0]
220 uF [T530Y227M010AT E006]	220 uF [TAJF227K006RNJ]	220 uF [TPSD227K004R004 0]	220 uF [TPSE227K010R007 0]
220 uF [T541D227M010AH 6510]	220 uF [TAJV227K016RNJ]	220 uF [TPSD227K004R005 0]	220 uF [TPSE227K010R010 0]
	220 uF [TAJW227K004RNJ]	220 uF [TPSD227K004R010 0]	
	220 uF [TAJY227K006RNJ]		

Multisim 14.1 Education Components

220 uF [TPSE227K010R012 5]	220 uF [TPSY227K010R010 0]	220 uH [SDR0906- 221KL]	220 uH [SRN6045- 221M]
220 uF [TPSE227K010R015 0]	220 uF [TPSY227K010R015 0]	220 uH [SDR1005- 221KL]	220 uH [SRR0603- 221KL]
220 uF [TPSE227K016R010 0]	220 uF [TPSY227K010R020 0]	220 uH [SDR1006- 221KL]	220 uH [SRR0604- 221KL]
220 uF [TPSE227K016R015 0]	220 uF [TRJD227K010RRJ]	220 uH [SDR1030- 221K]	220 uH [SRR0735A- 221M]
220 uF [TPSV227K016R005 0]	220 uF [TRJE227K010RRJ]	220 uH [SDR1045- 221K]	220 uH [SRR0745A- 221M]
220 uF [TPSV227K016R007 5]	220 uH [SDE0805A- 221K]	220 uH [SDR1305- 221K]	220 uH [SRR0804- 221K]
220 uF [TPSV227K016R010 0]	220 uH [SDE1006A- 221K]	220 uH [SDR1307- 221KL]	220 uH [SRR0805- 221K]
220 uF [TPSV227K016R015 0]	220 uH [SDR0302- 221KL]	220 uH [SDR1307A-221K]	220 uH [SRR0905- 221K]
220 uF [TPSV227K016R015 0]	220 uH [SDR0403- 221KL]	220 uH [SDR1806- 221KL]	220 uH [SRR0906- 221YL]
220 uF [TPSV227K016R015 0]	220 uH [SDR0503- 221KL]	220 uH [SDR6603- 221M]	220 uH [SRR0908- 221YL]
220 uF [TPSY227K004R004 0]	220 uH [SDR0603- 221KL]	220 uH [SDR7030- 221K]	220 uH [SRR1003- 221M]
220 uF [TPSY227K006R010 0]	220 uH [SDR0604- 221KL]	220 uH [SDR7045- 221K]	220 uH [SRR1005- 221K]
220 uF [TPSY227K006R015 0]	220 uH [SDR0703- 221KL]	220 uH [SRN1060- 221M]	220 uH [SRR1205- 221KL]
	220 uH [SDR0805- 221KL]	220 uH [SRN4018- 221M]	220 uH [SRR1206- 221KL]
		220 uH [SRN4026- 221M]	220 uH [SRR1208- 221KL]

Multisim 14.1 Education Components

220 uH [SRR1210-221M]	220 uH [SRU1038A-221Y]	221 Ohm [CR0603-FX-2210ELF]	226 Ohm [CR0603-FX-2260ELF]
220 uH [SRR1210A-221M]	220 uH [SRU1048-221Y]	221 Ohm [CR0603-FX-2210HLF]	226 Ohm [CR0805-FX-2260ELF]
220 uH [SRR1240-221K]	220 uH [SRU1048A-221Y]	221 Ohm [CR0805-FX-2210ELF]	226 Ohm [CR1206-FX-2260ELF]
220 uH [SRR1260-221K]	220 uH [SRU6025-221Y]	221 Ohm [CR0805-FX-2210GLF]	226 Ohm [CR2010-FX-2260ELF]
220 uH [SRR1260A-221K]	220 uH [SRU6025A-221Y]	221 Ohm [CR1206-FX-2210ELF]	226 Ohm [CRT1206-FZ-2260ELF]
220 uH [SRR1280-221K]	221 kOhm [CR0402-FX-2213GLF]	221 Ohm [CR2512-FX-2210ELF]	22GQ100
220 uH [SRR1806-221M]	221 kOhm [CR0603-FX-2213ELF]	221 Ohm [CRM1206-FX-2210ELF]	23 kOhm [4608X-101-233LF]
220 uH [SRR4028-221Y]	221 kOhm [CR0805-FX-2213ELF]	226 kOhm [CR0402-FX-2263GLF]	23.2 kOhm [CR0402-FX-2322GLF]
220 uH [SRR5018-221Y]	221 kOhm [CR1206-FX-2213ELF]	226 kOhm [CR0603-FX-2263ELF]	23.2 kOhm [CR0603-FX-2322ELF]
220 uH [SRR5028-221Y]	221 kOhm [CRT0603-AZ-2213ELF]	226 kOhm [CR0805-FX-2263ELF]	23.2 kOhm [CR0805-FX-2322ELF]
220 uH [SRR6028-221Y]	221 Ohm [CAT16-2210F4LF]	226 kOhm [CR1206-FX-2263ELF]	23.2 kOhm [CRT0402-BY-2322GLF]
220 uH [SRR6603-221ML]	221 Ohm [CAY16-2210F4LF]	226 Ohm [CAY16-2260F4LF]	23.2 kOhm [CRT0805-BY-2322ELF]
220 uH [SRR7032-221M]	221 Ohm [CR0402-FX-2210GLF]		

Multisim 14.1 Education Components

23.2 kOhm [CRT0805-CX- 2322ELF]	23.7 kOhm [CRT0805-FV- 2372ELF]	237 kOhm [CR0603-FX- 2373ELF]	24 kOhm [4308H- 101-243]
23.2 Ohm [CR0603- FX-23R2ELF]	23.7 Ohm [CR0402- FX-23R7GLF]	237 kOhm [CR0805-FX- 2373ELF]	24 kOhm [4308M- 102-243]
23.2 Ohm [CR1206- FX-23R2ELF]	23.7 Ohm [CR0603- FX-23R7ELF]	237 kOhm [CR1206-FX- 2373ELF]	24 kOhm [4308M- 102-243LF]
23.7 kOhm [CR0402-FX- 2372GLF]	23.7 Ohm [CR0805- FX-23R7ELF]	237 kOhm [CR1206-FX- 2373ELF]	24 kOhm [4608X- 101-243LF]
23.7 kOhm [CR0603-FX- 2372ELF]	23.7 Ohm [CR1206- FX-23R7ELF]	237 kOhm [CRT0805-BY- 2373ELF]	24 kOhm [CAT16- 2402F4LF]
23.7 kOhm [CR0805-FX- 2372ELF]	232 kOhm [CR0402-FX- 2323GLF]	237 Ohm [CR0402- FX-2370GLF]	24 kOhm [CAY10- 243J4LF]
23.7 kOhm [CR1206-FX- 2372ELF]	232 kOhm [CR0603-FX- 2323ELF]	237 Ohm [CR0603- FX-2370ELF]	24 kOhm [CAY16- 243J4LF]
23.7 kOhm [CRM2010-FX- 2372ELF]	232 kOhm [CR0805-FX- 2323ELF]	237 Ohm [CR0805- FX-2370ELF]	24 kOhm [CAY16- 243J8LF]
23.7 kOhm [CRM2512-FT- 2372ELF]	232 kOhm [CR1206-FX- 2323ELF]	237 Ohm [CRT0402-FZ- 2370GLF]	24 kOhm [CR0201- FW-2402GLF]
23.7 kOhm [CRT0603-BX- 2372ELF]	232 Ohm [CR0603- FX-2320ELF]	24 kOhm [4114R-1- 243]	24 kOhm [CR0402- FX-2402GLF]
23.7 kOhm [CRT0603-BX- 2372LF]	232 Ohm [CR0805- FX-2320ELF]	24 kOhm [4114R-1- 243LF]	24 kOhm [CR0603- FX-2402ELF]
23.7 kOhm [CRT0603-BX- 2372LF]	232 Ohm [CR1206- FX-2320ELF]	24 kOhm [4116R-1- 243]	24 kOhm [CR0603- JW-243ELF]
23.7 kOhm [CRT0805-BZ- 2372ELF]	237 kOhm [CR0402-FX- 2373GLF]	24 kOhm [4116R-1- 243LF]	24 kOhm [CR0805- FX-2402ELF]
			24 kOhm [CR0805- JW-243ELF]

Multisim 14.1 Education Components

24 kOhm [CR1206-FX-2402ELF]	24 Ohm [4114R-1-240LF]	24 Ohm [CR0603-JW-240ELF]	24 pF [C0402C240K4GACTU]
24 kOhm [CR1206-JW-243ELF]	24 Ohm [4116R-1-240LF]	24 Ohm [CR0603-JW-240GLF]	24 pF [C0402C240K5GACTU]
24 kOhm [CRM2010-FT-2402ELF]	24 Ohm [CAT10-240J4LF]	24 Ohm [CR0805-FX-24R0ELF]	24 pF [C0603C240K2GACTU]
24 kOhm [CRS2010-FX-2402ELF]	24 Ohm [CAT16-240J4GLF]	24 Ohm [CR1206-FX-24R0ELF]	24 pF [C0805C240K5GACTU]
24 mOhm [PWR1913WR024J]	24 Ohm [CAT25-240JALF]	24 Ohm [CR2010-JW-240ELF]	24 pF [C1206C240KBGACTU]
24 mOhm [PWR1913WR024JE]	24 Ohm [CAY10-240J2LF]	24 Ohm [CRM2512-FX-24R0ELF]	24 pF [C1210C240KBGACTU]
24 mOhm [PWR2615WR024J]	24 Ohm [CAY10-240J4LF]	24 Ohm [PWR2010W24R0JE]	24 pF [C1812C240KBGACTU]
24 mOhm [PWR2615WR024JE]	24 Ohm [CAY16-240J4LF]	24 Ohm [PWR3014W24R0JE]	24 pF [C1825C240KBGACTU]
24 mOhm [PWR4525WR024J]	24 Ohm [CAY16-240J8LF]	24 Ohm [PWR4318W24R0JE]	24 pF [C1825C240KCGACTU]
24 mOhm [PWR4525WR024JE]	24 Ohm [CAY17-240JALF]	24 Ohm [PWR5322W24R0JE]	
24 mOhm [PWR6327WR024J]	24 Ohm [CR0402-FX-24R0GLF]		
24 mOhm [PWR6327WR024JE]	24 Ohm [CR0402-JW-240GLF]		
24 Ohm [4114R-1-240]	24 Ohm [CR0603-FX-24R0ELF]		

Multisim 14.1 Education Components

24 pF [C2225C240KBGAC TU]	24.9 kOhm [CR0603-FX- 2492ELF]	24.9 Ohm [CAT16- 24R9F4LF]	240 kOhm [CAY16- 244J4LF]
24.3 kOhm [CR0402-FX- 2432GLF]	24.9 kOhm [CR0805-FX- 2492ELF]	24.9 Ohm [CAY16- 24R9F4LF]	240 kOhm [CHV1206-FX- 2403ELF]
24.3 kOhm [CR0603-FX- 2432ELF]	24.9 kOhm [CR1206-FX- 2492ELF]	24.9 Ohm [CR0201- FW-24R9GLF]	240 kOhm [CR0402-FX- 2403GLF]
24.3 kOhm [CR0805-FX- 2432ELF]	24.9 kOhm [CR2512-FX- 2492ELF]	24.9 Ohm [CR0603- FX-24R9ELF]	240 kOhm [CR0603-FX- 2403ELF]
24.3 kOhm [CR1206-FX- 2432ELF]	24.9 kOhm [CRM2512-FX- 2492ELF]	24.9 Ohm [CR0603- FX-24R9GLF]	240 kOhm [CR0603-JW- 244ELF]
24.3 Ohm [CR0402- FX-24R3GLF]	24.9 kOhm [CRT0402-BY- 2492GLF]	24.9 Ohm [CR0805- FX-24R9ELF]	240 kOhm [CR0805-FX- 2403ELF]
24.3 Ohm [CR0603- FX-24R3ELF]	24.9 kOhm [CRT0402-FZ- 2492GLF]	24.9 Ohm [CR1206- FX-24R9ELF]	240 kOhm [CR0805-JW- 244ELF]
24.3 Ohm [CR0805- FX-24R3ELF]	24.9 kOhm [CRT0603-BY- 2492ELF]	24.9 Ohm [CRM2512-FX- 24R9ELF]	240 kOhm [CR1206-FX- 2403ELF]
24.3 Ohm [CR1206- FX-24R3ELF]	24.9 kOhm [CRT0603-PW- 2492ELF]	24.9 Ohm [CRT0402-BY- 24R9GLF]	240 kOhm [CR1206-JW- 244ELF]
24.9 kOhm [CAT16- 2492F4LF]	24.9 kOhm [CRT0805-DY- 2492ELF]	24.9 Ohm [CRT0603-BY- 24R9ELF]	240 kOhm [CRT1206-BY- 2403ELF]
24.9 kOhm [CAY16- 2492F4LF]	24.9 kOhm [CRT1206-BY- 2492ELF]	24.9 Ohm [CRT1206-DY- 24R9ELF]	240 mOhm [CRL0603-FW- R240ELF]
24.9 kOhm [CR0402-FX- 2492GLF]			

Multisim 14.1 Education Components

240 mOhm [CRL0603-JW- R240ELF]	240 nH [SRN2010- R24M]	240 Ohm [4609X- AP1-241LF]	240 Ohm [CR0805- JW-241ELF]
240 mOhm [CRL0805-FW- R240ELF]	240 nH [SRN2012- R24M]	240 Ohm [4816P-2- 241]	240 Ohm [CR1206- FX-2400ELF]
240 mOhm [CRL0805-JW- R240ELF]	240 nH [SRN2510- R24M]	240 Ohm [4816P-2- 241LF]	240 Ohm [CR1206- JW-241ELF]
240 mOhm [CRL1206-FW- R240ELF]	240 nH [SRN2512- R24M]	240 Ohm [CAT10- 241J4LF]	240 Ohm [CR2010- JW-241ELF]
240 mOhm [CRL1206-JW- R240ELF]	240 Ohm [4114R-1- 241]	240 Ohm [CAT16- 2400F4LF]	240 Ohm [CRM1206-FX- 2400ELF]
240 mOhm [CRL2010-FW- R240ELF]	240 Ohm [4114R-2- 241]	240 Ohm [CAT16- 241J4LF]	240 Ohm [CRT0402-DZ- 2400GLF]
240 mOhm [CRL2010-JW- R240ELF]	240 Ohm [4116R-1- 241LF]	240 Ohm [CAT25- 241JALF]	240 Ohm [PWR220T-20- 2400F]
240 mOhm [CRL2512-FW- R240ELF]	240 Ohm [4116R-2- 241]	240 Ohm [CAY10- 241J4LF]	240 Ohm [PWR263S-35- 2400J]
240 mOhm [CRL2512-JW- R240ELF]	240 Ohm [4308R- 101-241]	240 Ohm [CAY16- 241J4LF]	240 pF [C0402C241K1HACT U]
240 mOhm [CRM2010-FX- R240ELF]	240 Ohm [4308R- 102-241]	240 Ohm [CR0402- FX-2400GLF]	240 pF [C0402C241K3HACT U]
240 mOhm [CRM2512-FX- R240ELF]	240 Ohm [4308R- 102-241LF]	240 Ohm [CR0402- JW-241GLF]	240 pF [C0402C241K5HACT U]
	240 Ohm [4310R- 101-241]	240 Ohm [CR0603- FX-2400ELF]	240 pF [C0603C241K5GACT U]
	240 Ohm [4310R- 101-241]	240 Ohm [CR0603- JW-241ELF]	
	240 Ohm [4606X- 101-241LF]	240 Ohm [CR0603- FX-2400ELF]	
	240 Ohm [4608X- 102-241LF]	240 Ohm [CR0603- JW-241GLF]	
		240 Ohm [CR0805- FX-2400ELF]	

Multisim 14.1 Education Components

240 pF [C0805C241K5GACT U]	243 Ohm [CAY16- 2430F4LF]	249 kOhm [CR1206-FX- 2493ELF]	249 Ohm [CR0805- FX-2490ELF]
240 pF [C1206C241KBGAC TU]	243 Ohm [CR0402- FX-2430GLF]	249 kOhm [CRT0603-BY- 2493ELF]	249 Ohm [CR1206- FX-2490ELF]
240 pF [C1210C241KBGAC TU]	243 Ohm [CR0603- FX-2430ELF]	249 kOhm [CRT0805-BY- 2493ELF]	249 Ohm [CR2512- FX-2490ELF]
240 pF [C1812C241KBGAC TU]	243 Ohm [CR1206- FX-2430ELF]	249 mOhm [PWR1913WR249J]	249 Ohm [CRM0805-FX- 2490ELF]
240 pF [C1825C241KBGAC TU]	243 Ohm [CRT0805-BY- 2430ELF]	249 mOhm [PWR1913WR249J]	249 Ohm [CRM2512-FX- 2490ELF]
240 pF [C2220C241KBGAC TU]	2462	249 mOhm [PWR2615WR249J]	249 Ohm [CRT0603-BY- 2490ELF]
240 pF [C2225C241KBGAC TU]	2466	249 mOhm [PWR2615WR249J]	249 Ohm [CRM2512-FX- 2490ELF]
240 pF [C2225C241KBGAC TU]	2468	249 mOhm [PWR2615WR249J]	249 Ohm [CRM2512-FX- 2490ELF]
240 pF [C2225C241KBGAC TU]	2477	249 mOhm [PWR4525WR249J]	249 Ohm [CRM2512-FX- 2490ELF]
243 kOhm [CR0402-FX- 2433GLF]	2481	249 mOhm [PWR4525WR249J]	249 Ohm [CRM2512-FX- 2490ELF]
243 kOhm [CR0603-FX- 2433ELF]	249 kOhm [CR0201-FW- 2493GLF]	249 mOhm [PWR4525WR249J]	25 kOhm [4116R-1- 253]
243 kOhm [CR0603-FX- 2433ELF]	249 kOhm [CR0402-FX- 2493GLF]	249 mOhm [PWR6327WR249J]	25 kOhm [4116R-2- 253]
243 kOhm [CR0805-FX- 2433ELF]	249 kOhm [CR0603-FX- 2493ELF]	249 mOhm [PWR6327WR249J]	25 kOhm [CRM2512-FX- 2490ELF]
243 kOhm [CR1206-FX- 2433ELF]	249 kOhm [CR0805-FX- 2493ELF]	249 Ohm [CR0402- FX-2490GLF]	25 kOhm [PWR163S-25- 2502F]
		249 Ohm [CR0603- FX-2490ELF]	

Multisim 14.1 Education Components

25 kOhm [PWR163S-25- 2502J]	25 mOhm [PWR4412- 2SCR0250J]	25 Ohm [PWR221T-30- 25R0J]	25.5 Ohm [CAT16- 25R5F4LF]
25 kOhm [PWR6327W2502JE]	25 mOhm [PWR4412- 2SDR0250F]	25 Ohm [PWR263S-20- 25R0J]	25.5 Ohm [CR0402- FX-25R5GLF]
25 mOhm [CRA2512-FZ- R025ELF]	25 Ohm [4116R-1- 250]	25.5 kOhm [CR0402-FX- 2552GLF]	25.5 Ohm [CR0603- FX-25R5ELF]
25 mOhm [CRA2512-JZ- R025ELF]	25 Ohm [4116R-1- 250LF]	25.5 kOhm [CR0603-FX- 2552ELF]	25.5 Ohm [CR1206- FX-25R5ELF]
25 mOhm [CRF2512-FZ- R025ELF]	25 Ohm [4310M- 102-250]	25.5 kOhm [CR0805-FX- 2552ELF]	25.5 Ohm [PWR4525W25R5F]
25 mOhm [PWR163S-25- R025J]	25 Ohm [4310M- 102-250LF]	25.5 kOhm [CR0805-FX- 2552ELF]	25_AMP
25 mOhm [PWR163S-25- R025J]	25 Ohm [4420P- T01-250]	25.5 kOhm [CR1206-FX- 2552ELF]	250 mOhm [CRM2512-FX- R250ELF]
25 mOhm [PWR163S-25- R025JE]	25 Ohm [4816P-1- 250]	25.5 kOhm [CRM2512-FX- 2552ELF]	250 mOhm [PWR163S-25- R250F]
25 mOhm [PWR220T-35- R025J]	25 Ohm [PWR163S-25- 25R0FE]	25.5 kOhm [CRT0402-BY- 2552GLF]	250 mOhm [PWR163S-25- R250FE]
25 mOhm [PWR221T-30- R025J]	25 Ohm [PWR220T-20- 25R0F]	25.5 kOhm [CRT0805-BW- 2552ELF]	250 mOhm [PWR163S-25- R250J]
25 mOhm [PWR4412- 2SBR0250F]	25 Ohm [PWR220T-35- 25R0J]	25.5 kOhm [CRT0805-BY- 2552ELF]	250 mOhm [PWR2010WR250JE]
25 mOhm [PWR4412- 2SCR0250F]	25 Ohm [PWR221T-30- 25R0F]	25.5 kOhm [CRT1206-BW- 2552ELF]	250 mOhm [PWR221T-30- R250F]

Multisim 14.1 Education Components

250 mOhm [PWR263S-35- R250F]	250 Ohm [PWR263S-35- 2500FE]	255 Ohm [CRT1206-BY- 2550ELF]	26.1 Ohm [CRM2512-FX- 26R1ELF]
250 mOhm [PWR4318WR250JE]	250 Ohm [PWR263S-35- 2500JE]	26.1 kOhm [CR0402-FX- 2612GLF]	26.1 Ohm [CRT0402-FZ- 26R1GLF]
250 mOhm [PWR5322WR250JE]	250 Ohm [PWR4318W2500JE]	26.1 kOhm [CR0603-FX- 2612ELF]	26.1 Ohm [CRT0805-CX- 26R1ELF]
250 Ohm [4116R-1- 251]	2-534206-0	26.1 kOhm [CR0805-FX- 2612ELF]	26.7 kOhm [CAY16- 2672F4LF]
250 Ohm [4310R- 101-251]	255 kOhm [CR0402-FX- 2553GLF]	26.1 kOhm [CR1206-FX- 2612ELF]	26.7 kOhm [CR0402-FX- 2672GLF]
250 Ohm [4310R- 101-251LF]	255 kOhm [CR0603-FX- 2553ELF]	26.1 kOhm [CRT0603-FZ- 2612ELF]	26.7 kOhm [CR0603-FX- 2672ELF]
250 Ohm [4420P-1- 251]	255 kOhm [CR0805-FX- 2553ELF]	26.1 kOhm [CRT0805-BY- 2612ELF]	26.7 kOhm [CR0805-FX- 2672ELF]
250 Ohm [4609X- 101-251LF]	255 kOhm [CR1206-FX- 2553ELF]	26.1 Ohm [CR0402- FX-26R1GLF]	26.7 kOhm [CR1206-FX- 2672ELF]
250 Ohm [CRT1206-PW- 2500ELF]	255 kOhm [CRT0805-BY- 2553ELF]	26.1 Ohm [CR0603- FX-26R1ELF]	26.7 kOhm [CRT0805-BY- 2672ELF]
250 Ohm [PWR163S-25- 2500FE]	255 Ohm [CR0603- FX-2550ELF]	26.1 Ohm [CR0805- FX-26R1ELF]	26.7 kOhm [CRT1206-BY- 2672ELF]
250 Ohm [PWR220T-35- 2500J]	255 Ohm [CR0805- FX-2550ELF]	26.1 Ohm [CR1206- FX-26R1ELF]	26.7 Ohm [CAY16- 26R7F4LF]
250 Ohm [PWR263S-35- 2500F]	255 Ohm [CR2010- FX-2550ELF]	26.1 Ohm [CRM1206-FX- 26R1ELF]	26.7 Ohm [CR0402- FX-26R7GLF]

Multisim 14.1 Education Components

26.7 Ohm [CR0603-FX-26R7ELF]	261 Ohm [CRM1206-FX-2610ELF]	267 Ohm [CR1206-FX-2670ELF]	27 kOhm [4308R-101-273]
26.7 Ohm [CR0805-FX-26R7ELF]	261 Ohm [CRT0402-FZ-2610GLF]	27 kOhm [4114R-1-273]	27 kOhm [4308R-101-273LF]
26.7 Ohm [CR1206-FX-26R7ELF]	261 Ohm [CRT0603-BY-2610ELF]	27 kOhm [4114R-1-273LF]	27 kOhm [4308R-102-273]
261 kOhm [CR0402-FX-2613GLF]	267 kOhm [CR0402-FX-2673GLF]	27 kOhm [4114R-2-273]	27 kOhm [4308R-102-273LF]
261 kOhm [CR0603-FX-2613ELF]	267 kOhm [CR0603-FX-2673ELF]	27 kOhm [4116R-1-273]	27 kOhm [4309R-101-273]
261 kOhm [CR0805-FX-2613ELF]	267 kOhm [CR0805-FX-2673ELF]	27 kOhm [4116R-1-273LF]	27 kOhm [4309R-101-273LF]
261 kOhm [CR1206-FX-2613ELF]	267 kOhm [CR1206-FX-2673ELF]	27 kOhm [4116R-2-273]	27 kOhm [4310M-101-273]
261 kOhm [CRT0805-CX-2613ELF]	267 kOhm [CRM2512-FX-2673ELF]	27 kOhm [4116R-2-273LF]	27 kOhm [4310M-101-273LF]
261 Ohm [CAY16-2610F4LF]	267 Ohm [CAY16-2670F4LF]	27 kOhm [4306M-101-273]	27 kOhm [4310R-101-273]
261 Ohm [CR0402-FX-2610GLF]	267 Ohm [CR0402-FX-2670GLF]	27 kOhm [4306R-101-273]	27 kOhm [4310R-101-273LF]
261 Ohm [CR0603-FX-2610ELF]	267 Ohm [CR0603-FX-2670ELF]	27 kOhm [4306R-101-273LF]	27 kOhm [4310R-102-273]
261 Ohm [CR0805-FX-2610ELF]	267 Ohm [CR0805-FX-2670ELF]	27 kOhm [4306R-102-273]	27 kOhm [4310R-102-273LF]
261 Ohm [CR1206-FX-2610ELF]		27 kOhm [4306R-102-273LF]	27 kOhm [4420P-2-273]
		27 kOhm [4308H-101-273]	27 kOhm [4420P-T02-273]
		27 kOhm [4308H-101-273LF]	27 kOhm [4604X-101-273LF]

Multisim 14.1 Education Components

27 kOhm [4604X-102-273LF]	27 kOhm [4611X-101-273LF]	27 kOhm [CAT16-273J2LF]	27 kOhm [CR0805-JW-273ELF]
27 kOhm [4605X-101-273LF]	27 kOhm [4814P-T01-273]	27 kOhm [CAT16-273J4LF]	27 kOhm [CR0805-JW-273GLF]
27 kOhm [4606X-101-273LF]	27 kOhm [4814P-T01-273LF]	27 kOhm [CAT25-273JALF]	27 kOhm [CR1206-FX-2702ELF]
27 kOhm [4606X-102-273LF]	27 kOhm [4816P-1-273]	27 kOhm [CAY10-273J4LF]	27 kOhm [CR1206-JW-273ELF]
27 kOhm [4607M-101-273LF]	27 kOhm [4816P-1-273F]	27 kOhm [CAY16-2702F4LF]	27 kOhm [CR2512-JW-273ELF]
27 kOhm [4607X-101-273LF]	27 kOhm [4816P-1-273LF]	27 kOhm [CAY16-273J4LF]	27 kOhm [CRT0805-BY-2702ELF]
27 kOhm [4608H-102-273LF]	27 kOhm [4816P-2-273]	27 kOhm [CAY16-273J8LF]	27 mF [C0402C279K5GACTU]
27 kOhm [4608X-101-273LF]	27 kOhm [4816P-2-273LF]	27 kOhm [CR0201-FW-2702GLF]	27 mF [C0805C279KBGAC TU]
27 kOhm [4608X-102-273LF]	27 kOhm [4816P-T01-273]	27 kOhm [CR0402-FX-2702GLF]	27 mOhm [PWR1913WR027J]
27 kOhm [4608X-AP2-273LF]	27 kOhm [4816P-T01-273LF]	27 kOhm [CR0402-JW-273GLF]	27 mOhm [PWR1913WR027JE]
27 kOhm [4609X-101-273LF]	27 kOhm [4816P-T02-273]	27 kOhm [CR0603-FX-2702ELF]	27 mOhm [PWR2615WR027J]
27 kOhm [4609X-AP1-273LF]	27 kOhm [4816P-T02-273LF]	27 kOhm [CR0603-FX-2702GLF]	27 mOhm [PWR2615WR027JE]
27 kOhm [4610M-101-273LF]	27 kOhm [4820P-2-273F]	27 kOhm [CR0603-JW-273ELF]	27 mOhm [PWR2615WR027JE]
27 kOhm [4610X-101-273LF]	27 kOhm [4820P-2-273LF]	27 kOhm [CR0805-FX-2702ELF]	27 mOhm [PWR4525WR027J]
27 kOhm [4610X-102-273LF]	27 kOhm [CAT16-2702F4LF]	27 kOhm [CR0805-FX-2702GLF]	

Multisim 14.1 Education Components

27 mOhm [PWR4525WR027JE]	27 nF [C0603C273K4RACT U]	27 nF [C0805F273K3RACT U]	27 nF [C1210C273K1RACT U]
27 mOhm [PWR6327WR027J]	27 nF [C0603C273K5RACT U]	27 nF [C0805F273K4RACT U]	27 nF [C1210C273K2RACT U]
27 mOhm [PWR6327WR027JE]	27 nF [C0805C273K1RACT U]	27 nF [C0805F273K5RACT U]	27 nF [C1210C273K3GACT U]
27 nF [C0402C273K3RACT U]	27 nF [C0805C273K2RACT U]	27 nF [C1206C273K1HACT U]	27 nF [C1210C273K3HACT U]
27 nF [C0402C273K4RACT U]	27 nF [C0805C273K3HACT U]	27 nF [C1206C273K1RACT U]	27 nF [C1210C273K5GACT U]
27 nF [C0402C273K8PACT U]	27 nF [C0805C273K3RACT U]	27 nF [C1206C273K3HACT U]	27 nF [C1210C273K5HACT U]
27 nF [C0402C273K8RACT U]	27 nF [C0805C273K4RACT U]	27 nF [C1206C273K5HACT U]	27 nF [C1210C273K5RACT U]
27 nF [C0402C273K9PACT U]	27 nF [C0805C273K5RACT U]	27 nF [C1206C273K5RACT U]	27 nF [C1210C273KARACT U]
27 nF [C0402C273K9RACT U]	27 nF [C0805C273K8RACT U]	27 nF [C1206C273KARACT U]	27 nF [C1812C273K1HACT U]
27 nF [C0603C273K1RACT U]	27 nF [C0805C273M5UAC TU]	27 nF [C1210C273K1GACT U]	27 nF [C1812C273K1RACT U]
27 nF [C0603C273K3RACT U]	27 nF [C0805F273K1RACT U]	27 nF [C1210C273K1HACT U]	27 nF [C1812C273K5HACT U]

Multisim 14.1 Education Components

27 nF [C1825C273K1GACT U]	27 Ohm [4114R-2- 270]	27 Ohm [4310R- 102-270LF]	27 Ohm [4814P- T01-270]
27 nF [C1825C273K5GACT U]	27 Ohm [4116R-1- 270]	27 Ohm [4416P-1- 270]	27 Ohm [4816P-1- 270]
27 nF [C2220C273K1GACT U]	27 Ohm [4116R-1- 270LF]	27 Ohm [4416P- T01-270]	27 Ohm [4816P-1- 270LF]
27 nF [C2220C273K1GACT U]	27 Ohm [4116R-2- 270]	27 Ohm [4420P-1- 270]	27 Ohm [4816P-2- 270]
27 nF [C2220C273K2GACT U]	27 Ohm [4306H- 102-270]	27 Ohm [4420P- T01-270]	27 Ohm [4816P-2- 270LF]
27 nF [GMC5.7272K250J3 1TR12]	27 Ohm [4306R- 101-270]	27 Ohm [4606X- 101-270LF]	27 Ohm [4816P- T01-270]
27 nF [GMC5.7273K50J31 TR12]	27 Ohm [4306R- 101-270LF]	27 Ohm [4606X- 102-270LF]	27 Ohm [4816P- T01-270LF]
27 nF [GMC5.7273K50J31 TR12]	27 Ohm [4306R- 102-270]	27 Ohm [4608H- 102-270LF]	27 Ohm [4816P- T02-270]
27 nF [GMC7.3272K250K3 1TR12]	27 Ohm [4308R- 101-270]	27 Ohm [4608X- 101-270LF]	27 Ohm [4816P- T02-270LF]
27 nF [GMC7.3272K63K31 TR12]	27 Ohm [4308R- 101-270LF]	27 Ohm [4608X- 102-270LF]	27 Ohm [4820P-1- 270]
27 nF [GMC7.3272K63K31 TR12]	27 Ohm [4308R- 102-270]	27 Ohm [4608X- AP1-270LF]	27 Ohm [4820P- T01-270]
27 nF [GMC7.3273K63K31 TR12]	27 Ohm [4308R- 102-270LF]	27 Ohm [4609X- 101-270LF]	27 Ohm [4820P- T01-270LF]
27 nF [MMC5.7273K100J 31TR12]	27 Ohm [4310R- 101-270]	27 Ohm [4610X- 101-270LF]	27 Ohm [CAT10- 270J4LF]
27 Ohm [4114R-1- 270]	27 Ohm [4310R- 101-270LF]	27 Ohm [4610X- 102-270LF]	27 Ohm [CAT16- 270J4GLF]
27 Ohm [4114R-1- 270LF]	27 Ohm [4310R- 102-270]	27 Ohm [4814P-1- 270]	27 Ohm [CAT16- 270J4LF]

Multisim 14.1 Education Components

27 Ohm [CAT16-270J8LF]	27 Ohm [CR1206-FX-27R0ELF]	27 Ohm [PWR221T-30-27R0F]	27 pF [C0603C270K1GACTU]
27 Ohm [CAT16-27R0F4LF]	27 Ohm [CR1206-JW-270ELF]	27 Ohm [PWR263S-20-27R0F]	27 pF [C0603C270K2GACTU]
27 Ohm [CAT16-27R0F8LF]	27 Ohm [CR2010-JW-270ELF]	27 Ohm [PWR263S-20-27R0J]	27 pF [C0603C270K5GACTU]
27 Ohm [CAT25-270JALF]	27 Ohm [CR2512-FX-27R0ELF]	27 Ohm [PWR263S-35-27R0F]	27 pF [C0805C270K1GACTU]
27 Ohm [CAY10-270J4LF]	27 Ohm [CR2512-JW-270ELF]	27 Ohm [PWR263S-35-27R0FE]	27 pF [C0805C270K2GACTU]
27 Ohm [CAY16-270J4LF]	27 Ohm [CRM1206-JW-270ELF]	27 Ohm [PWR263S-35-27R0J]	27 pF [C0805C270K3GACTU]
27 Ohm [CAY16-270J8LF]	27 Ohm [FW20A27R0JA]	27 pF [C0201C270K3GACTU]	27 pF [C0805C270K4GACTU]
27 Ohm [CAY16-27R0F4LF]	27 Ohm [PWR163S-25-27R0F]	27 pF [C0402C270K3GACTU]	27 pF [C1206C270K1GACTU]
27 Ohm [CR0201-JW-270GLF]	27 Ohm [PWR163S-25-27R0FE]	27 pF [C0402C270K4GACTU]	27 pF [C1206C270K2GACTU]
27 Ohm [CR0402-FX-27R0GLF]	27 Ohm [PWR163S-25-27R0J]	27 pF [C0402C270K5GACTU]	27 pF [C1206C270K5GACTU]
27 Ohm [CR0402-JW-270GLF]	27 Ohm [PWR220T-20-27R0F]	27 pF [C0402C270K8GACTU]	
27 Ohm [CR0603-FX-27R0ELF]	27 Ohm [PWR220T-20-27R0J]		
27 Ohm [CR0603-JW-270ELF]	27 Ohm [PWR220T-35-27R0J]		
27 Ohm [CR0805-FX-27R0ELF]			
27 Ohm [CR0805-JW-270ELF]			

Multisim 14.1 Education Components

27 pF [C1206C270KBGAC TU]	27 uH [SDE0805A- 270M]	27 uH [SRP6540- 270M]	27 uH [SRR1240- 270M]
27 pF [C1210C270KBGAC TU]	27 uH [SDE1006A- 270M]	27 uH [SRR0735A- 270M]	27 uH [SRR1260- 270M]
27 pF [C1812C270KBGAC TU]	27 uH [SDR0302- 270ML]	27 uH [SRR0745A- 270M]	27 uH [SRR1260A- 270M]
27 pF [C1812C270KBGAC TU]	27 uH [SDR0403- 270KL]	27 uH [SRR0804- 270Y]	27 uH [SRR1280- 270M]
27 pF [C1812C270KHGAC TU]	27 uH [SDR0503- 270ML]	27 uH [SRR0805- 270Y]	27 uH [SRR4018- 270Y]
27 pF [C1825C270KBGAC TU]	27 uH [SDR0603- 270ML]	27 uH [SRR0905- 270M]	27 uH [SRR4028- 270Y]
27 pF [C2220C270KBGAC TU]	27 uH [SDR0604- 270YL]	27 uH [SRR0906- 270ML]	27 uH [SRR5018- 270Y]
27 pF [C2225C270KBGAC TU]	27 uH [SDR0703- 270KL]	27 uH [SRR0908- 270ML]	27 uH [SRR5028- 270Y]
27 pF [C2225C270KBGAC TU]	27 uH [SDR0805- 270KL]	27 uH [SRR1003- 270M]	27 uH [SRR6028- 270Y]
27 pF [CA064C270K5GAC TU]	27 uH [SDR0906- 270KL]	27 uH [SRR1005- 270Y]	27 uH [SRR6038- 270Y]
27 pF [CA064C270K8GAC TU]	27 uH [SDR1006- 270KL]	27 uH [SRR1205- 270ML]	27 uH [SRR6040A- 270M]
27 uF [EEHZA1V270P]	27 uH [SDR1105- 270ML]	27 uH [SRR1206- 270ML]	27 uH [SRR7045- 270M]
27 uH [SDE0403A- 270M]	27 uH [SDR1307- 270ML]	27 uH [SRR1208- 270ML]	27 uH [SRU1038- 270Y]
27 uH [SDE0604A- 270M]	27 uH [SDR1307A- 270M]	27 uH [SRR1210- 270M]	27 uH [SRU8043- 270Y]
	27 uH [SRN5040- 270M]	27 uH [SRR1210A- 270M]	27.4 kOhm [CR0402-FX- 2742GLF]

Multisim 14.1 Education Components

27.4 kOhm [CR0603-FX- 2742ELF]	270 kOhm [4116R- 1-274LF]	270 kOhm [4310R- 102-274LF]	270 kOhm [4814P- 1-274]
27.4 kOhm [CR0805-FX- 2742ELF]	270 kOhm [4116R- 2-274]	270 kOhm [4416P- 1-274]	270 kOhm [4816P- 1-274]
27.4 kOhm [CR1206-FX- 2742ELF]	270 kOhm [4306H- 101-274]	270 kOhm [4416P- 2-274]	270 kOhm [4816P- 1-274LF]
27.4 kOhm [CR1206-FX- 2742ELF]	270 kOhm [4306H- 102-274]	270 kOhm [4416P- T01-274]	270 kOhm [4816P- 2-274]
27.4 kOhm [CRT0805-BY- 2742ELF]	270 kOhm [4306R- 101-274]	270 kOhm [4416P- T02-274]	270 kOhm [4816P- 2-274LF]
27.4 Ohm [CAY16- 27R4F4LF]	270 kOhm [4306R- 101-274LF]	270 kOhm [4604M- 101-274LF]	270 kOhm [4816P- T01-274]
27.4 Ohm [CR0402- FX-27R4GLF]	270 kOhm [4306R- 102-274]	270 kOhm [4604X- 102-274LF]	270 kOhm [4816P- T01-274LF]
27.4 Ohm [CR0603- FX-27R4ELF]	270 kOhm [4306R- 102-274LF]	270 kOhm [4606X- 101-274LF]	270 kOhm [4816P- T02-274]
27.4 Ohm [CR0805- FX-27R4ELF]	270 kOhm [4308R- 101-274]	270 kOhm [4606X- 102-274LF]	270 kOhm [4816P- T02-274LF]
27.4 Ohm [CR1206- FX-27R4ELF]	270 kOhm [4308R- 101-274LF]	270 kOhm [4608X- 101-274LF]	270 kOhm [CAT16- 2703F4LF]
27.4 Ohm [CRM1206-FX- 27R4ELF]	270 kOhm [4308R- 102-274]	270 kOhm [4608X- 102-274LF]	270 kOhm [CAT16- 274J4LF]
270 kOhm [4114R- 1-274]	270 kOhm [4308R- 102-274LF]	270 kOhm [4609H- 101-274LF]	270 kOhm [CAT25- 274JALF]
270 kOhm [4114R- 1-274LF]	270 kOhm [4310R- 101-274]	270 kOhm [4609X- 101-274LF]	270 kOhm [CAY16- 274J4LF]
270 kOhm [4116R- 1-274]	270 kOhm [4310R- 101-274LF]	270 kOhm [4610X- 101-274LF]	270 kOhm [CAY16- 274J8LF]
	270 kOhm [4310R- 102-274]	270 kOhm [4610X- 102-274LF]	270 kOhm [CR0402-FX- 2703GLF]

Multisim 14.1 Education Components

270 kOhm [CR0603-FX- 2703ELF]	270 mOhm [CRL0805-FW- R270ELF]	270 mOhm [PWR263S-35- R270F]	270 nF [C1206C274K1RACT U]
270 kOhm [CR0603-JW- 274ELF]	270 mOhm [CRL0805-JW- R270ELF]	270 mOhm [PWR263S-35- R270FE]	270 nF [C1206C274K3RACT U]
270 kOhm [CR0603-JW- 274GLF]	270 mOhm [CRL1206-FW- R270ELF]	270 nF [C0603C274K4PACT U]	270 nF [C1206C274K4RACT U]
270 kOhm [CR0805-FX- 2703ELF]	270 mOhm [CRL1206-JW- R270ELF]	270 nF [C0603C274K4RACT U]	270 nF [C1206C274K5RACT U]
270 kOhm [CR0805-JW- 274ELF]	270 mOhm [CRL2010-FW- R270ELF]	270 nF [C0603C274K8PACT U]	270 nF [C1206F274K3RACT U]
270 kOhm [CR0805-JW- 274GLF]	270 mOhm [CRL2010-JW- R270ELF]	270 nF [C0603C274K8RACT U]	270 nF [C1206F274K4RACT U]
270 kOhm [CR1206-FX- 2703ELF]	270 mOhm [CRL2512-FW- R270ELF]	270 nF [C0603C274K9PACT U]	270 nF [C1206F274K5RACT U]
270 kOhm [CR1206-JW- 274ELF]	270 mOhm [CRM2010-FX- R270ELF]	270 nF [C0603C274K9RACT U]	270 nF [C1210C274K1RACT U]
270 kOhm [CRM2512-JW- 274ELF]	270 mOhm [CRM2512-FX- R270ELF]	270 nF [C0805C274K3RACT U]	270 nF [C1210C274K3RACT U]
270 mOhm [CRL0603-FW- R270ELF]	270 mOhm [PWR220T-20- R270F]	270 nF [C0805C274K4RACT U]	270 nF [C1210C274K5RACT U]
270 mOhm [CRL0603-JW- R270ELF]	270 mOhm [PWR220T-35- R270F]	270 nF [C0805C274K8RACT U]	270 nF [C1210C274M5UAC TU]

Multisim 14.1 Education Components

270 nF [C1210F274K1RACT U]	270 nF [C1825C274K1RACT U]	270 nF [MDC10274K400A5 7P7TUBE]	270 nF [MDS15274K50B53 P3TUBE]
270 nF [C1210F274K3RACT U]	270 nF [C1825C274K5RACT U]	270 nF [MDC10274K400A5 7P8TUBE]	270 nF [MMC16.5274K400 C31TR24]
270 nF [C1210F274K4RACT U]	270 nF [C2220C274K1GACT U]	270 nF [MDC10274K50A52 P3TUBE]	270 nF [MMC7.3274K63K3 5TR12]
270 nF [C1210F274K5RACT U]	270 nF [C2220C274K5GACT U]	270 nF [MDC15274K100B5 3P3TUBE]	270 nH [SRP1038A- R27M]
270 nF [C1812C274K1RACT U]	270 nF [C2220C274K5RACT U]	270 nF [MDC15274K250B5 3P3TUBE]	270 Ohm [4114R-1- 271]
270 nF [C1812C274K5RACT U]	270 nF [C2225C274K1RACT U]	270 nF [MDC15274K400B5 3P3TUBE]	270 Ohm [4114R-1- 271LF]
270 nF [C1812C274KARACT U]	270 nF [C2225C274K2RACT U]	270 nF [MDC15274K50B53 P3TUBE]	270 Ohm [4114R-2- 271LF]
270 nF [C1812F274K1RACT U]	270 nF [C2225C274K5RACT U]	270 nF [MDK15274K100B5 3P3TUBE]	270 Ohm [4116R-1- 271]
270 nF [C1812F274K2RACT U]	270 nF [GMC7.3274K63K35 TR12]	270 nF [MDK15274K400B5 3P3TUBE]	270 Ohm [4116R-2- 271]
270 nF [C1812F274K3RACT U]	270 nF [MDC10274K100A5 2P3TUBE]	270 nF [MDK15274K50B53 P3TUBE]	270 Ohm [4116R-2- 271LF]
270 nF [C1812F274K5RACT U]	270 nF [MDC10274K250A5 2P3TUBE]	270 nF [MDS15274K400B5 3P3TUBE]	270 Ohm [4304M- 102-271]
			270 Ohm [4306M- 101-271]

Multisim 14.1 Education Components

270 Ohm [4306R-101-271]	270 Ohm [4310R-102-271]	270 Ohm [4606X-101-271LF]	270 Ohm [4614X-102-271LF]
270 Ohm [4306R-101-271LF]	270 Ohm [4310R-102-271LF]	270 Ohm [4606X-102-271LF]	270 Ohm [4814P-1-271]
270 Ohm [4306R-102-271]	270 Ohm [4416P-2-271]	270 Ohm [4606X-AP1-271LF]	270 Ohm [4814P-1-271LF]
270 Ohm [4306R-102-271LF]	270 Ohm [4416P-T01-271]	270 Ohm [4607X-101-271LF]	270 Ohm [4814P-2-271]
270 Ohm [4308M-102-271]	270 Ohm [4416P-T02-271]	270 Ohm [4608M-102-271LF]	270 Ohm [4814P-T01-271]
270 Ohm [4308R-101-271]	270 Ohm [4420P-1-271]	270 Ohm [4608X-101-271LF]	270 Ohm [4814P-T01-271LF]
270 Ohm [4308R-101-271LF]	270 Ohm [4420P-2-271]	270 Ohm [4608X-102-271LF]	270 Ohm [4814P-T02-271]
270 Ohm [4308R-102-271]	270 Ohm [4420P-2-271LF]	270 Ohm [4609H-101-271LF]	270 Ohm [4814P-T02-271LF]
270 Ohm [4308R-102-271LF]	270 Ohm [4420P-T01-271]	270 Ohm [4609M-101-271LF]	270 Ohm [4816P-1-271]
270 Ohm [4309R-101-271]	270 Ohm [4420P-T02-271]	270 Ohm [4609X-101-271LF]	270 Ohm [4816P-1-271LF]
270 Ohm [4309R-101-271LF]	270 Ohm [4420P-T04-271]	270 Ohm [4610H-101-271LF]	270 Ohm [4816P-2-271]
270 Ohm [4310M-101-271]	270 Ohm [4604M-101-271LF]	270 Ohm [4610X-101-271LF]	270 Ohm [4816P-2-271LF]
270 Ohm [4310M-102-271]	270 Ohm [4604X-101-271LF]	270 Ohm [4610X-102-271LF]	270 Ohm [4816P-T01-271]
270 Ohm [4310R-101-271]	270 Ohm [4604X-102-271LF]	270 Ohm [4611X-101-271LF]	270 Ohm [4816P-T01-271LF]
270 Ohm [4310R-101-271LF]	270 Ohm [4605X-101-271LF]	270 Ohm [4612X-102-271LF]	270 Ohm [4816P-T02-271]

Multisim 14.1 Education Components

270 Ohm [4816P-T02-271LF]	270 Ohm [CR0402-FX-2700GLF]	270 Ohm [CRM2512-JW-271ELF]	270 pF [C0603C271K1RACTU]
270 Ohm [4820P-1-271]	270 Ohm [CR0402-JW-271GLF]	270 Ohm [PWR263S-35-2700J]	270 pF [C0603C271K2RACTU]
270 Ohm [4820P-2-271]	270 Ohm [CR0603-FX-2700ELF]	270 Ohm [PWR5322W2700FE]	270 pF [C0603C271K3RACTU]
270 Ohm [4820P-T01-271]	270 Ohm [CR0603-FX-2700GLF]	270 pF [C0402C271K1HACTU]	270 pF [C0603C271K4GACTU]
270 Ohm [4820P-T02-271]	270 Ohm [CR0603-JW-271ELF]	270 pF [C0402C271K3HACTU]	270 pF [C0603C271K4RACTU]
270 Ohm [CAT10-271J4LF]	270 Ohm [CR0603-JW-271GLF]	270 pF [C0402C271K3RACTU]	270 pF [C0603C271K5GACTU]
270 Ohm [CAT16-2700F4LF]	270 Ohm [CR0805-FX-2700ELF]	270 pF [C0402C271K4RACTU]	270 pF [C0805C271K1GACTU]
270 Ohm [CAT16-271J4LF]	270 Ohm [CR0805-FX-2700GLF]	270 pF [C0402C271K5GACTU]	270 pF [C0805C271K1RACTU]
270 Ohm [CAT16-271J8LF]	270 Ohm [CR0805-JW-271ELF]	270 pF [C0402C271K5HACTU]	270 pF [C0805C271K2GACTU]
270 Ohm [CAT25-271JALF]	270 Ohm [CR1206-FX-2700ELF]	270 pF [C0402C271K8RACTU]	
270 Ohm [CAY10-271J4LF]	270 Ohm [CR1206-JW-271ELF]		
270 Ohm [CAY16-2700F4LF]	270 Ohm [CR2512-JW-271ELF]		
270 Ohm [CAY16-271J2LF]	270 Ohm [CRM1206-FX-2700ELF]		
270 Ohm [CAY16-271J4LF]	270 Ohm [CRM2512-FX-2700ELF]		
270 Ohm [CAY16-271J8LF]			

Multisim 14.1 Education Components

270 pF [C0805C271K4RACT U]	270 pF [C2225C271KBGAC TU]	270 uF [EEFLT0E271R]	270 uH [SDR0603- 271KL]
270 pF [C0805C271K5GACT U]	270 uF [10SVPC270M]	270 uF [EEFST0E271R]	270 uH [SDR0604- 271KL]
270 pF [C0805C271K5RACT U]	270 uF [16SEPC270M]	270 uF [EEFSX0D271E4]	270 uH [SDR0703- 271KL]
270 pF [C0805C271K5RACT U]	270 uF [16SEPC270MX]	270 uF [EEFSX0D271ER]	270 uH [SDR0805- 271KL]
270 pF [C1206C271K1GACT U]	270 uF [16SVPC270M]	270 uF [EEFSX0D271XE]	270 uH [SDR0906- 271KL]
270 pF [C1206C271K2GACT U]	270 uF [2TPSF270M6E]	270 uF [EEFSX0E271E7]	270 uH [SDR1006- 271KL]
270 pF [C1206C271K2GACT U]	270 uF [2TPSF270M9G]	270 uF [EEFSX0G271ER]	270 uH [SDR1307- 271KL]
270 pF [C1206C271K5GACT U]	270 uF [A700X277M002AT E010]	270 uF [EEHZA1V271P]	270 uH [SDR1307A-271K]
270 pF [C1206C271KBGAC TU]	270 uF [A700X277M002AT E015]	270 uF [EEHZC1V271P]	270 uH [SRR0735A- 271M]
270 pF [C1210C271KBGAC TU]	270 uF [A700X277M004AT E010]	270 uF [ETPSF270M6E]	270 uH [SRR0745A- 271M]
270 pF [C1812C271KBGAC TU]	270 uF [A700X277M004AT E015]	270 uH [SDE0805A- 271K]	270 uH [SRR0804- 271K]
270 pF [C1812C271KBGAC TU]	270 uF [A700X277M004AT E015]	270 uH [SDE1006A- 271K]	270 uH [SRR0805- 271K]
270 pF [C1825C271KBGAC TU]	270 uF [EEFCX0D271XR]	270 uH [SDR0302- 271KL]	270 uH [SRR0905- 271K]
270 pF [C1825C271KBGAC TU]	270 uF [EEFCX0D271XR]	270 uH [SDR0403- 271KL]	270 uH [SRR0906- 271YL]
270 pF [C2220C271KBGAC TU]	270 uF [EEFCX0G271R]	270 uH [SDR0503- 271KL]	270 uH [SRR0908- 271YL]

Multisim 14.1 Education Components

270 uH [SRR1003-271Y]	274 kOhm [CR0805-FX-2743ELF]	27C010V120	27C128-20L
270 uH [SRR1005-271K]	274 kOhm [CR1206-FX-2743ELF]	27C010V150	27C128-20P
270 uH [SRR1205-271KL]	274 kOhm [CRT0603-BY-2743ELF]	27C010V70	27C128-25L
270 uH [SRR1206-271KL]	274 Ohm [CAY16-2740F4LF]	27C010V90	27C128-25P
270 uH [SRR1208-271KL]	274 Ohm [CR0402-FX-2740GLF]	27C020N100	27C128N120
270 uH [SRR1210-271M]	274 Ohm [CR0603-FX-2740ELF]	27C020N120	27C128N150
270 uH [SRR1210A-271M]	274 Ohm [CR0805-FX-2740ELF]	27C020N150	27C128N200
270 uH [SRR1240-271K]	274 Ohm [CR0402-FX-2740GLF]	27C020Q100	27C128N90
270 uH [SRR1260-271K]	274 Ohm [CR1206-FX-2740ELF]	27C020Q120	27C128Q120
270 uH [SRR1260A-271K]	274 Ohm [CRT0402-FZ-2740GLF]	27C020Q150	27C128Q150
270 uH [SRR1280-271K]	27C010N120	27C020V100	27C128Q200
270 uH [SRR4028-271Y]	27C010N150	27C020V120	27C128Q90
270 uH [SRR7045-271M]	27C010N70	27C020V150	27C128V120
274 kOhm [CR0402-FX-2743GLF]	27C010Q120	27C040N120	27C128V150
274 kOhm [CR0603-FX-2743ELF]	27C010Q150	27C040N150	27C128V200
	27C010Q70	27C040Q120	27C128V90
	27C010Q90	27C040Q150	27C16BQ150
		27C040V120	27C16BQ200
		27C040V150	27C256-12L
		27C128-12L	27C256-12P
		27C128-12P	27C256-15L
		27C128-15L	27C256-15P
		27C128-15P	27C256-20L
		27C128-17L	27C256-20P
		27C128-17P	27C256N100

Multisim 14.1 Education Components

27C256N120	27C64-12L	28 kOhm [CR1206-FX-2802ELF]	28.7 Ohm [CR0603-FX-28R7ELF]
27C256N150	27C64-12P		
27C256N200	27C64-15L	28 kOhm [CR1206-FX-2802ELFF]	28.7 Ohm [CR0805-FX-28R7ELF]
27C256N90	27C64-15P	28 kOhm	28.7 Ohm [CR1206-FX-28R7ELF]
27C256Q100	27C64-17L	[CRT0805-FY-2802ELF]	
27C256Q120	27C64-17P		28.7 Ohm
27C256Q150	27C64-20L	28 Ohm [CAY16-28R0F4LF]	[CRT0402-FZ-28R7GLF]
27C256Q200	27C64-20P	28 Ohm [CR0402-FX-28R0GLF]	280 kOhm
27C256Q90	27C64-25L		[CR0402-FX-2803GLF]
27C256V100	27C64-25P	28 Ohm [CR0603-FX-28R0ELF]	280 kOhm
27C256V120	27C64E200-883		[CR0603-FX-2803ELF]
27C256V150	27C64E250-883	28 Ohm [CR0805-FX-28R0ELF]	
27C256V200	27C64E350-883	28 Ohm [CR1206-FX-28R0ELF]	280 kOhm
27C256V90	27C64N150		[CR0805-FX-2803ELF]
27C32BQ150	27C64N200	28.7 kOhm	280 kOhm
27C32BQ200	27C64Q150	[CR0402-FX-2872GLF]	[CR1206-FX-2803ELF]
27C512N120	27C64Q200	28.7 kOhm	280 Ohm [CR0402-FX-2800GLF]
27C512N150	27C64Q200-883	[CR0603-FX-2872ELF]	
27C512N90	27C64Q250-883	28.7 kOhm	280 Ohm [CR0603-FX-2800ELF]
27C512Q120	27C64Q350-883	[CR0805-FX-2872ELF]	
27C512Q150	28 kOhm [CR0402-FX-2802GLF]	28.7 kOhm	280 Ohm [CR0805-FX-2800ELF]
27C512Q90		[CR1206-FX-2872ELF]	280 Ohm [CR1206-FX-2800ELF]
27C512V120	28 kOhm [CR0603-FX-2802ELF]	28.7 kOhm	280 Ohm
27C512V150	28 kOhm [CR0805-FX-2802ELF]	[CRT0805-BY-2872ELF]	[CRT0805-BY-2800ELF]
27C512V90			

Multisim 14.1 Education Components

282834-2	287 Ohm	29.4 Ohm [CR0805-	294 kOhm
282834-4	[CRM2512-FX-	FX-29R4ELF]	[CR0805-FX-
282834-5	287 Ohm	29.4 Ohm [CR1206-	2943ELF]
282834-8	[CRT0402-FZ-	FX-29R4ELF]	294 kOhm
284258	2870GLF]	290 mOhm	[CR1206-FX-
287 kOhm [CAT16-	287 Ohm	[PWR1913WR290J]	2943ELF]
2873F4LF]	[CRT1206-BY-	290 mOhm	294 Ohm [CR0402-
287 kOhm	2870ELF]	[PWR1913WR290JE	FX-2940GLF]
[CR0402-FX-	28V_7.5W]	294 Ohm [CR0603-
2873GLF]	29 kOhm [4116R-1-	290 mOhm	FX-2940ELF]
287 kOhm	293]	[PWR2615WR290J]	294 Ohm [CR0603-
[CR0603-FX-	29 kOhm [4116R-1-	290 mOhm	FX-2940GLF]
2873ELF]	293LF]	[PWR2615WR290JE	294 Ohm [CR0805-
287 kOhm	29.4 kOhm]	FX-2940ELF]
[CR0805-FX-	[CR0402-FX-	290 mOhm	294 Ohm [CR1206-
2873ELF]	2942GLF]	[PWR4525WR290J]	FX-2940ELF]
287 kOhm	29.4 kOhm	290 mOhm	2A3
[CR1206-FX-	[CR0603-FX-	[PWR4525WR290JE	2K8RAM
2873ELF]	2942ELF]]	2N1599
287 Ohm [CR0201-	29.4 kOhm	290 mOhm	2N2222A
FW-2870GLF]	[CR0805-FX-	[PWR6327WR290J]	2N2573
287 Ohm [CR0402-	2942ELF]	290 mOhm	2N2574
FX-2870GLF]	29.4 kOhm	[PWR6327WR290JE	2N2575
287 Ohm [CR0603-	[CR1206-FX-]	2N2576
FX-2870ELF]	2942ELF]	292303-1	2N2577
287 Ohm [CR0805-	29.4 kOhm	292304-1	2N2578
FX-2870ELF]	[CRT0805-BY-	294 kOhm	2N2579
287 Ohm [CR1206-	2942ELF]	[CR0402-FX-	2N2608
FX-2870ELF]	29.4 Ohm [CR0402-	2943GLF]	
	FX-29R4GLF]	294 kOhm	
	29.4 Ohm [CR0603-	[CR0603-FX-	
	FX-29R4ELF]	2943ELF]	

Multisim 14.1 Education Components

2N2609	2N3670	2N3897	2N4062
2N2712	2N3684	2N3898	2N4084
2N2714	2N3685	2N3899	2N4091
2N2923	2N3686	2N3903	2N4092
2N2924	2N3687	2N3904	2N4093
2N2925	2N3702	2N3904G	2N4117A
2N3055A	2N3703	2N3905	2N4118A
2N3055AG	2N3707	2N3906	2N4119A
2N3055G	2N3711	2N3906G	2N4123
2N3370	2N3771G	2N3921	2N4124
2N3390	2N3772G	2N3922	2N4125
2N3391	2N3773G	2N3954	2N4126
2N3391A	2N3821	2N3954A	2N4167
2N3392	2N3822	2N3955	2N4168
2N3393	2N3823	2N3955A	2N4169
2N3394	2N3824	2N3956	2N4170
2N3414	2N3858A	2N3957	2N4171
2N3415	2N3859	2N3958	2N4172
2N3416	2N3859A	2N3966	2N4173
2N3417	2N3860	2N3967	2N4174
2N3442G	2N3870	2N3970	2N4183
2N3458	2N3871	2N3971	2N4184
2N3459	2N3872	2N3972	2N4185
2N3668	2N3873	2N4058	2N4186
2N3669	2N3896	2N4061	2N4187

Multisim 14.1 Education Components

2N4188	2N4392	2N4861	2N5089
2N4189	2N4393	2N4861A	2N5103
2N4190	2N4400	2N4918G	2N5105
2N4199	2N4401	2N4919G	2N5114
2N4200	2N4402	2N4920G	2N5115
2N4201	2N4403	2N4921G	2N5116
2N4202	2N4409	2N4922G	2N5168
2N4203	2N4410	2N4923G	2N5169
2N4204	2N4416	2N5018	2N5170
2N4220	2N4416A	2N5019	2N5171
2N4220A	2N4424	2N5020	2N5172
2N4221	2N4441	2N5021	2N5191G
2N4221A	2N4442	2N5038G	2N5192G
2N4222	2N4443	2N5045	2N5194G
2N4222A	2N4444	2N5046	2N5195G
2N4223	2N4856	2N5047	2N5196
2N4286	2N4856A	2N5060	2N5197
2N4289	2N4857	2N5061	2N5199
2N4291	2N4857A	2N5062	2N5209
2N4338	2N4858	2N5063	2N5210
2N4339	2N4858A	2N5064	2N5223
2N4340	2N4859	2N5078	2N5224
2N4341	2N4859A	2N5086	2N5226
2N4381	2N4860	2N5087	2N5227
2N4391	2N4860A	2N5088	2N5232

Multisim 14.1 Education Components

2N5232A	2N5517	2N5684G	2N6042G
2N5302G	2N5518	2N5686G	2N6043G
2N5354	2N5519	2N5769	2N6045G
2N5355	2N5520	2N5771	2N6052G
2N5358	2N5521	2N5817	2N6071
2N5365	2N5522	2N5830	2N6073BG
2N5366	2N5523	2N5883G	2N6107G
2N5397	2N5524	2N5884G	2N6109G
2N5398	2N5545	2N5885G	2N6111G
2N5400	2N5550	2N5886G	2N6145
2N5401	2N5550G	2N6027	2N6146
2N5432	2N5550RLRPG	2N6027G	2N6147
2N5433	2N5551	2N6027RL1G	2N6157
2N5434	2N5556	2N6027RLRAG	2N6158
2N5444	2N5557	2N6028	2N6159
2N5445	2N5558	2N6028G	2N6160
2N5446	2N5564	2N6028RLRAG	2N6161
2N5447	2N5565	2N6028RLRMG	2N6162
2N5452	2N5566	2N6028RLRPG	2N6163
2N5454	2N5567	2N6034G	2N6164
2N5484	2N5568	2N6035G	2N6165
2N5485	2N5571	2N6036G	2N6167
2N5486	2N5572	2N6038G	2N6168
2N5515	2N5655G	2N6039G	2N6169
2N5516	2N5657G	2N6040G	2N6170

Multisim 14.1 Education Components

2N6171	2N6398	2N7002BKW	2PA1774QM
2N6172	2N6399	2N7002CK	2PA1774QMB
2N6173	2N6400	2N7002DW	2PA1774R
2N6174	2N6401	2N7002E	2PA1774RM
2N6284G	2N6402	2N7002ET1G	2PA1774RMB
2N6286G	2N6403	2N7002F	2PA1774S
2N6287G	2N6404	2N7002K	2PA1774SM
2N6288G	2N6405	2N7002K-T1-GE3	2PA1774SMB
2N6292G	2N6487G	2N7002LT1G	2PB1219AQ
2N6338G	2N6488G	2N7002LT3G	2PB1219AR
2N6341G	2N6490G	2N7002P	2PB1219AS
2N6342	2N6491G	2N7002PS	2PB1424
2N6343	2N6667G	2N7002PT	2PB709ARL
2N6344	2N6715	2N7002PV	2PB709ART
2N6345	2N6727	2N7002PW	2PB709ARW
2N6346	2N7000	2N7269	2PB709ASL
2N6347	2N7000G	2P1S	2PB709ASW
2N6348	2N7000RLRAG	2P2S	2PB709BRL
2N6349	2N7002	2P3S	2PB709BSL
2N6387G	2N7002BK	2P4S	2PB710ARL
2N6388G	2N7002BKM	2P5S	2PB710ASL
2N6394	2N7002BKMB	2PA1576Q	2PC4081Q
2N6395	2N7002BKS	2PA1576R	2PC4081R
2N6396	2N7002BKT	2PA1576S	2PC4081S
2N6397	2N7002BKV	2PA1774Q	2PC4617Q

Multisim 14.1 Education Components

2PC4617QM	2SA1507T	2SC2873	2SD1623T-TD-E
2PC4617QMB	2SA1774G	2SC3332S	2SD1628F-TD-E
2PC4617R	2SA1774T1G	2SC3332S-AA	2SD1628F-TD-H
2PC4617RM	2SA2126-E	2SC3649S-TD-E	2SD1628G-TD-E
2PC4617RMB	2SA2126-H	2SC3649S-TD-H	2SD1628G-TD-H
2PD1820AR	2SA2126-TL-E	2SC3649T-TD-E	2SD1805F-E
2PD1820AS	2SA2126-TL-H	2SC3649T-TD-H	2SD1805F-TL-E
2PD2150	2SA2205-E	2SC3733	2SD1805G-E
2PD601ARL	2SA2205-TL-E	2SC4617G	2SD1805G-TL-E
2PD601ART	2SA2210-1E	2SC4617T1G	2SD1815S-E
2PD601ARW	2SA2222SG	2SC5566-TD-E	2SD1815S-TL-E
2PD601ASL	2SA733	2SC5658M3T5G	2SD1815T-E
2PD601ASW	2SA952	2SC5706-E	2SD1815T-TL-E
2PD601BRL	2SA953	2SC5706-H	2SJ517
2PD601BSL	2SA954	2SC5706-TL-E	2SJ652
2PD602AQL	2SB1204S-E	2SC5706-TL-H	2SJ652-RA11
2PD602ARL	2SB1204S-TL-E	2SC5964-TD-E	2SJ661-E
2PD602ASL	2SB1205S-TL-E	2SC5964-TD-H	2SJ665-DL-E
2SA1015	2SB1205T-TL-E	2SC5994-TD-E	2SK117
2SA1020	2SC1815	2SC6082	2SK170
2SA1213	2SC2001	2SC6097-E	2SK192A
2SA1416S-TD-E	2SC2120	2SC6097-TL-E	2SK208
2SA1416T-TD-E	2SC2240	2SC6144SG	2SK209
2SA1460	2SC2655	2SC945	2SK2394-6-TB-E
2SA1507S	2SC2786	2SD1623S-TD-E	2SK2553L

Multisim 14.1 Education Components

2SK2553S	2SK3746	3 kOhm [4306R-101-302LF]	3 kOhm [CR0402-FX-3001GLF]
2SK2978	2SK3746-1E		
2SK2980	2SK3747	3 kOhm [4308R-102-302]	3 kOhm [CR0402-JW-302GLF]
2SK3069	2SK3747-1E		
2SK3070L	2SK3748	3 kOhm [4310R-101-302]	3 kOhm [CR0603-FX-3001ELF]
2SK3070S	2SK3748-1E	3 kOhm [4310R-101-302LF]	3 kOhm [CR0603-JW-302ELF]
2SK30ATM	2SK3820-DL-E		
2SK3133	2SK3820-E	3 kOhm [4607X-101-302LF]	3 kOhm [CR0805-FX-3001ELF]
2SK3134	2SK4177-DL-1E	3 kOhm [4610X-101-302LF]	3 kOhm [CR0805-FX-3001GLF]
2SK3135	2SK536-TB-E		
2SK3136	2SWITCHCM	3 kOhm [4814P-1-302]	3 kOhm [CR0805-JW-302ELF]
2SK3140	2V7002LT1G		
2SK3141	2V7002LT3G	3 kOhm [4814P-2-302]	3 kOhm [CR1206-FX-3001ELF]
2SK3142	3 kOhm [4116R-1-302]	3 kOhm [4814P-2-302LF]	3 kOhm [CR1206-JW-302ELF]
2SK3203			
2SK3233	3 kOhm [4116R-1-302LF]	3 kOhm [4816P-1-302]	3 kOhm [CR2512-FX-3001ELF]
2SK330			
2SK3557-6-TB-E	3 kOhm [4304H-102-302]	3 kOhm [4816P-1-302LF]	3 kOhm [CR2512-JW-302ELF]
2SK3557-7-TB-E	3 kOhm [4304M-102-302]	3 kOhm [CAT16-302J4LF]	3 kOhm [CRM2512-FX-3001ELF]
2SK364			
2SK366	3 kOhm [4304M-102-302LF]	3 kOhm [CAT25-302JALF]	3 kOhm [CRM2512-JW-302ELF]
2SK367	3 kOhm [4306H-101-302]	3 kOhm [CAY10-302J4LF]	
2SK368			
2SK3703	3 kOhm [4306R-101-302]	3 kOhm [CAY16-302J4LF]	3 kOhm [CRT0603-FX-3001ELF]
2SK3704			3 kOhm [CRT0805-BY-3001ELF]

Multisim 14.1 Education Components

3 kOhm [CRT1206-BY-3001ELF]	3 mOhm [CRF2512-JX-R003ELF]	3 nF [C2225C302KBGAC TU]	3 Ohm [CRL0603-FW-3R00ELF]
3 kOhm [PWR220T-35-3001J]	3 nF [C0603C302K1HACT U]	3 Ohm [CAT10-3R0J4LF]	3 Ohm [CRL0603-JW-3R00ELF]
3 kOhm [PWR2615W3001FE]	3 nF [C0603C302K3HACT U]	3 Ohm [CAT16-3R0J2LF]	3 Ohm [CRL0805-FW-3R00ELF]
3 kOhm [PWR2615W3001J]	3 nF [C0603C302K5HACT U]	3 Ohm [CAT16-3R0J4LF]	3 Ohm [CRL0805-JW-3R00ELF]
3 kOhm [PWR2615W3001JE]	3 nF [C0805C302K1GACT U]	3 Ohm [CAY10-3R0J2LF]	3 Ohm [CRL2010-FW-3R00ELF]
3 kOhm [PWR263S-35-3001F]	3 nF [C0805C302K1HACT U]	3 Ohm [CAY16-3R0J2LF]	3 Ohm [CRL2010-JW-3R00ELF]
3 kOhm [PWR4525W3001J]	3 nF [C0805C302K3GACT U]	3 Ohm [CAY16-3R0J4LF]	3 Ohm [CRL2512-FW-3R00ELF]
3 MOhm [4116R-1-305LF]	3 nF [C0805C302K3HACT U]	3 Ohm [CR0402-J/-3R0GLF]	3 Ohm [CRM2512-JW-3R0ELF]
3 MOhm [CR0603-JW-305ELF]	3 nF [C0805C302K3HACT U]	3 Ohm [CR0603-J/-3R0ELF]	3 Ohm [CRT0805-DY-3R00ELF]
3 MOhm [CR0805-JW-305ELF]	3 nF [C0805C302K5HACT U]	3 Ohm [CR0603-J/-3R0GLF]	3 Ohm [CRT0805-FZ-3R00ELF]
3 MOhm [CR1206-JW-305ELF]	3 nF [C1825C302KBGAC TU]	3 Ohm [CR0805-J/-3R0ELF]	3 Ohm [PWR163S-25-3R00F]
3 mOhm [CRE2512-FZ-R003E-2]	3 nF [C2220C302KBGAC TU]	3 Ohm [CR1206-J/-3R0ELF]	3 Ohm [PWR163S-25-3R00FE]
3 mOhm [CRE2512-FZ-R003E-3]		3 Ohm [CR2010-J/-3R0ELF]	3 Ohm [PWR163S-25-3R00J]
3 mOhm [CRF2512-FX-R003ELF]		3 Ohm [CR2512-J/-3R0ELF]	3 Ohm [PWR220T-20-3R00F]

Multisim 14.1 Education Components

3 Ohm [PWR220T-20-3R00J]	3 uH [SRR1003-3R0M]	3.01 kOhm [CR1206-FX-3011ELF]	3.09 kOhm [CR1206-FX-3091ELF]
3 Ohm [PWR220T-35-3R00F]	3 uH [SRR1005-3R0M]	3.01 kOhm [CRM1206-FX-3011ELF]	3.09 MOhm [CR0603-FX-3094ELF]
3 Ohm [PWR221T-30-3R00F]	3 uH [SRR5018-3R0Y]	3.01 kOhm [CRT0402-FZ-3011GLF]	3.16 kOhm [CR0402-FX-3161GLF]
3 Ohm [PWR2615W3R00F]	3 uH [SRR5028-3R0Y]	3.01 kOhm [CRT0603-FZ-3011ELF]	3.16 kOhm [CR0603-FX-3161ELF]
3 Ohm [PWR2615W3R00FE]	3 uH [SRR6028-3R0Y]	3.01 kOhm [CRT0805-BY-3011ELF]	3.16 kOhm [CR0805-FX-3161ELF]
3 Ohm [PWR263S-20-3R00F]	3 uH [SRU1048-3R0Y]	3.01 kOhm [CRT0805-FZ-3011ELF]	3.16 kOhm [CR1206-FX-3161ELF]
3 Ohm [PWR263S-20-3R00FE]	3 uH [SRU1048A-3R0Y]	3.01 Ohm [CRM1206-FX-3R01ELF]	3.16 kOhm [CRT0402-FZ-3161GLF]
3 Ohm [PWR263S-20-3R00J]	3 uH [SRU2016-3R0Y]	3.01 Ohm [CRM2010-FX-3R01ELF]	3.16 kOhm [CRT0603-FX-3161ELF]
3 Ohm [PWR263S-20-3R00JE]	3 uH [SRU3014-3R0Y]	3.09 kOhm [CR0402-FX-3091GLF]	3.16 kOhm [CRT0603-FZ-3161ELF]
3 Ohm [PWR263S-35-3R00F]	3.01 kOhm [CAY16-3011F4LF]	3.09 kOhm [CR0603-FX-3091ELF]	3.16 kOhm [CRT1206-BY-3161ELF]
3 Ohm [PWR263S-35-3R00FE]	3.01 kOhm [CR0402-FX-3011GLF]	3.09 kOhm [CR0805-FX-3091ELF]	3.2 kOhm [4310R-101-322]
3 Ohm [PWR263S-35-3R00J]	3.01 kOhm [CR0603-FX-3011ELF]	3.09 kOhm [CR0805-FX-3091ELF]	3.2 uH [SRP1045-3R2M]
3 Ohm [PWR263S-35-3R00JE]	3.01 kOhm [CR0805-FX-3011ELF]		
3 Ohm [PWR4318W3R00JE]			
3 uH [SRN6028-3R0Y]			

Multisim 14.1 Education Components

3.24 kOhm [CR0402-FX- 3241GLF]	3.3 kOhm [4116R- 1-332LF]	3.3 kOhm [4308H- 102-332LF]	3.3 kOhm [4310R- 102-332]
3.24 kOhm [CR0603-FX- 3241ELF]	3.3 kOhm [4116R- 2-332]	3.3 kOhm [4308M- 101-332]	3.3 kOhm [4310R- 102-332LF]
3.24 kOhm [CR0805-FX- 3241ELF]	3.3 kOhm [4116R- 2-332LF]	3.3 kOhm [4308R- 101-332]	3.3 kOhm [4416P- 2-332]
3.24 kOhm [CR1206-FX- 3241ELF]	3.3 kOhm [4306H- 101-332LF]	3.3 kOhm [4308R- 101-332LF]	3.3 kOhm [4416P- T02-332]
3.24 kOhm [CR2010-FX- 3241ELF]	3.3 kOhm [4306H- 102-332]	3.3 kOhm [4308R- 102-332LF]	3.3 kOhm [4420P- 1-332]
3.24 kOhm [CRT0805-BY- 3241ELF]	3.3 kOhm [4306H- 102-332LF]	3.3 kOhm [4309R- 101-332]	3.3 kOhm [4420P- 2-332LF]
3.3 kOhm [4108R- 1-332]	3.3 kOhm [4306M- 102-332]	3.3 kOhm [4309R- 101-332LF]	3.3 kOhm [4420P- T02-332]
3.3 kOhm [4108R- 1-332LF]	3.3 kOhm [4306M- 102-332LF]	3.3 kOhm [4310H- 101-332]	3.3 kOhm [4604X- 101-332LF]
3.3 kOhm [4114R- 1-332]	3.3 kOhm [4306R- 101-332]	3.3 kOhm [4310H- 101-332LF]	3.3 kOhm [4604X- 102-332LF]
3.3 kOhm [4114R- 1-332LF]	3.3 kOhm [4306R- 101-332LF]	3.3 kOhm [4310H- 102-332]	3.3 kOhm [4605M- 101-332LF]
3.3 kOhm [4114R- 2-332]	3.3 kOhm [4306R- 102-332]	3.3 kOhm [4310M- 101-332]	3.3 kOhm [4605X- 101-332LF]
3.3 kOhm [4114R- 2-332LF]	3.3 kOhm [4306R- 102-332LF]	3.3 kOhm [4310M- 101-332LF]	3.3 kOhm [4605X- AP1-332LF]
3.3 kOhm [4116R- 1-332]	3.3 kOhm [4308H- 101-332]	3.3 kOhm [4310R- 101-332]	3.3 kOhm [4606H- 101-332LF]
	3.3 kOhm [4308H- 102-332]	3.3 kOhm [4310R- 101-332LF]	3.3 kOhm [4606X- 101-332LF]

Multisim 14.1 Education Components

3.3 kOhm [4606X-102-332LF]	3.3 kOhm [4610M-101-332LF]	3.3 kOhm [4816P-1-332LF]	3.3 kOhm [CAT16-3301F4LF]
3.3 kOhm [4606X-AP1-332LF]	3.3 kOhm [4610X-101-332LF]	3.3 kOhm [4816P-2-332]	3.3 kOhm [CAT16-3301F8LF]
3.3 kOhm [4607M-101-332LF]	3.3 kOhm [4610X-102-332LF]	3.3 kOhm [4816P-2-332LF]	3.3 kOhm [CAT16-332J4LF]
3.3 kOhm [4607X-101-332LF]	3.3 kOhm [4610X-AP1-332LF]	3.3 kOhm [4816P-T01-332]	3.3 kOhm [CAT16-332J8LF]
3.3 kOhm [4608H-101-332LF]	3.3 kOhm [4611X-101-332LF]	3.3 kOhm [4816P-T01-332LF]	3.3 kOhm [CAT25-332JALF]
3.3 kOhm [4608H-102-332LF]	3.3 kOhm [4612X-102-332LF]	3.3 kOhm [4816P-T02-332]	3.3 kOhm [CAY10-332J4LF]
3.3 kOhm [4608M-102-332LF]	3.3 kOhm [4814P-1-332]	3.3 kOhm [4816P-T02-332LF]	3.3 kOhm [CAY16-3301F4LF]
3.3 kOhm [4608X-101-332LF]	3.3 kOhm [4814P-1-332LF]	3.3 kOhm [4818P-2-332]	3.3 kOhm [CAY16-332J4LF]
3.3 kOhm [4608X-102-332LF]	3.3 kOhm [4814P-2-332]	3.3 kOhm [4818P-2-332LF]	3.3 kOhm [CAY16-332J8LF]
3.3 kOhm [4608X-AP1-332LF]	3.3 kOhm [4814P-2-332LF]	3.3 kOhm [4818P-T02-332]	3.3 kOhm [CAY17-332JALF]
3.3 kOhm [4608X-AP2-332LF]	3.3 kOhm [4814P-T01-332]	3.3 kOhm [4820P-2-332]	3.3 kOhm [CR0201-JW-332GLF]
3.3 kOhm [4609H-101-332LF]	3.3 kOhm [4814P-T01-332LF]	3.3 kOhm [4820P-2-332F]	3.3 kOhm [CR0402-FX-3301GLF]
3.3 kOhm [4609X-101-332LF]	3.3 kOhm [4814P-T02-332]	3.3 kOhm [4820P-T02-332]	3.3 kOhm [CR0402-JW-332GLF]
3.3 kOhm [4609X-AP1-332LF]	3.3 kOhm [4814P-T02-332LF]	3.3 kOhm [4820P-T02-332LF]	3.3 kOhm [CR0603-FX-3301ELF]
3.3 kOhm [4610H-101-332LF]	3.3 kOhm [4816P-1-332]	3.3 kOhm [CAT10-332J4LF]	3.3 kOhm [CR0603-FX-3301HLF]

Multisim 14.1 Education Components

3.3 kOhm [CR0603-JW-332ELF]	3.3 kOhm [CRT0603-DY-3301ELF]	3.3 kOhm [PWR263S-35-3301J]	3.3 MOhm [4609X-101-335LF]
3.3 kOhm [CR0603-JW-332GLF]	3.3 kOhm [CRT0603-PW-3301ELF]	3.3 kOhm [PWR4525W3301JE]	3.3 MOhm [4610X-101-335LF]
3.3 kOhm [CR0805-FX-3301ELF]	3.3 kOhm [CRT0805-DY-3301ELF]	3.3 kOhm [WS5M3301J]	3.3 MOhm [CAT25-335JALF]
3.3 kOhm [CR0805-FX-3301GLF]	3.3 kOhm [CRT0805-PV-3301ELF]	3.3 mH [SDR0503-332JL]	3.3 MOhm [CHV0603-FX-3304ELF]
3.3 kOhm [CR0805-JW-332ELF]	3.3 kOhm [CRT0805-PV-3301ELF]	3.3 mH [SDR0805-332KL]	3.3 MOhm [CHV0805-JW-335ELF]
3.3 kOhm [CR1206-FX-3301ELF]	3.3 kOhm [PWR163S-25-3301J]	3.3 mH [SDR0906-332KL]	3.3 MOhm [CHV1206-FX-3304ELF]
3.3 kOhm [CR1206-JW-332GLF]	3.3 kOhm [PWR220T-20-3301F]	3.3 mH [SDR1005-332KL]	3.3 MOhm [CHV2010-FX-3304ELF]
3.3 kOhm [CR2010-JW-332ELF]	3.3 kOhm [PWR220T-20-3301J]	3.3 mH [SRE6603-332M]	3.3 MOhm [CR0603-JW-335ELF]
3.3 kOhm [CR2512-FX-3301ELF]	3.3 kOhm [PWR221T-30-3301F]	3.3 mH [SRR0906-332YL]	3.3 MOhm [CR0805-JW-335ELF]
3.3 kOhm [CR2512-JW-332ELF]	3.3 kOhm [PWR263S-20-3301F]	3.3 mH [SRR0908-332YL]	3.3 MOhm [CR1206-JW-335ELF]
3.3 kOhm [CRM1206-FX-3301ELF]	3.3 kOhm [PWR263S-20-3301J]	3.3 mH [SRR1208-332KL]	3.3 nF [C0402C332K3RACT U]
3.3 kOhm [CRM1206-JW-332ELF]	3.3 kOhm [PWR263S-35-3301F]	3.3 mH [SRR6603-332ML]	3.3 nF [C0402C332K4RACT U]
3.3 kOhm [CRT0603-BY-3301ELF]		3.3 MOhm [4608X-102-335LF]	

Multisim 14.1 Education Components

3.3 nF [C0402C332K5RACT U]	3.3 nF [C0805C332K1GACT U]	3.3 nF [C0805C332K8GACT U]	3.3 nF [C1210C332K5RACT U]
3.3 nF [C0402C332K8RACT U]	3.3 nF [C0805C332K1HACT U]	3.3 nF [C0805C332KARACT U]	3.3 nF [C1825C332KBGAC TU]
3.3 nF [C0402C332K9RACT U]	3.3 nF [C0805C332K1RACT U]	3.3 nF [C1206C332K1GACT U]	3.3 nF [C2220C332KBGAC TU]
3.3 nF [C0603C332K1HACT U]	3.3 nF [C0805C332K2RACT U]	3.3 nF [C1206C332K1RACT U]	3.3 nF [C2225C332KBGAC TU]
3.3 nF [C0603C332K1RACT U]	3.3 nF [C0805C332K3GACT U]	3.3 nF [C1206C332K2RACT U]	3.3 nF [CA064C332K1RACT U]
3.3 nF [C0603C332K3GACT U]	3.3 nF [C0805C332K3HACT U]	3.3 nF [C1206C332K3RACT U]	3.3 nF [CA064C332K5RACT U]
3.3 nF [C0603C332K3HACT U]	3.3 nF [C0805C332K4GACT U]	3.3 nF [C1206C332K5GACT U]	3.3 nF [GMC5.7332K100J3 1TR12]
3.3 nF [C0603C332K3RACT U]	3.3 nF [C0805C332K4RACT U]	3.3 nF [C1206C332K5RACT U]	3.3 nF [GMC5.7332K50J31 TR12]
3.3 nF [C0603C332K4RACT U]	3.3 nF [C0805C332K5GACT U]	3.3 nF [C1210C332K1RACT U]	3.3 nF [GMC5.7333K100J3 3TR12]
3.3 nF [C0603C332K5HACT U]	3.3 nF [C0805C332K5HACT U]	3.3 nF [C1210C332K2GACT U]	3.3 nF [GMC7.3332K100K3 1TR12]
3.3 nF [C0603C332K5RACT U]	3.3 nF [C0805C332K5RACT U]	3.3 nF [C1210C332K5GACT U]	3.3 nF [GMC7.3332K400K3 1TR12]

Multisim 14.1 Education Components

3.3 nF [GMC7.3333K100K3 1TR12]	3.3 nF [MMC7.3332K400K 31TR12]	3.3 Ohm [CRL0603- FW-3R30ELF]	3.3 Ohm [PWR163S-25- 3R30F]
3.3 nF [GMC7.3333K250K3 5TR12]	3.3 nF [MMC7.3332K50K3 1TR12]	3.3 Ohm [CRL0603- JW-3R30ELF]	3.3 Ohm [PWR163S-25- 3R30J]
3.3 nF [GPC7.3332K160K3 1TR12]	3.3 nF [MMC7.3332K63K3 1TR12]	3.3 Ohm [CRL0805- FW-3R30ELF]	3.3 Ohm [PWR220T-20- 3R30F]
3.3 nF [GPC7.3332K400K3 1TR12]	3.3 nF [SPC7.3332K100K31 TR12]	3.3 Ohm [CRL1206- FW-3R30ELF]	3.3 Ohm [PWR220T-20- 3R30J]
3.3 nF [GPC7.3332K630K3 3TR12]	3.3 nF [SPC7.3332K250K31 TR12]	3.3 Ohm [CRL1206- JW-3R30ELF]	3.3 Ohm [PWR220T-35- 3R30F]
3.3 nF [GPC7.3332K63K31 TR12]	3.3 nF [SPC7.3332K400K33 TR12]	3.3 Ohm [CRL2010- JW-3R30ELF]	3.3 Ohm [PWR220T-35- 3R30J]
3.3 nF [MMC5.7332K100J 31TR12]	3.3 nF [SPC7.3332K630K35 TR12]	3.3 Ohm [CRL2512- FW-3R30ELF]	3.3 Ohm [PWR221T-30- 3R30F]
3.3 nF [MMC5.7332K250J 31TR12]	3.3 Ohm [CR0402- J/-3R3GLF]	3.3 Ohm [CRM2010-JW- 3R3ELF]	3.3 Ohm [PWR221T-30- 3R30J]
3.3 nF [MMC5.7332K50J3 1TR12]	3.3 Ohm [CR0603- J/-3R3ELF]	3.3 Ohm [CRM2512-JW- 3R3ELF]	3.3 Ohm [PWR2615W3R30F]
3.3 nF [MMC7.3332K100K 31TR12]	3.3 Ohm [CR0805- J/-3R3ELF]	3.3 Ohm [CRS0805- JW-3R3ELF]	3.3 Ohm [PWR2615W3R30F E]
3.3 nF [MMC7.3332K250K 31TR12]	3.3 Ohm [CR1206- J/-3R3ELF]	3.3 Ohm [CRS1206- FW-3R30ELF]	3.3 Ohm [PWR2615W3R30J]
	3.3 Ohm [CR2010- J/-3R3ELF]	3.3 Ohm [CRS2512- FW-3R30ELF]	3.3 Ohm [PWR263S-20- 3R30F]
	3.3 Ohm [CR2512- J/-3R3ELF]		

Multisim 14.1 Education Components

3.3 Ohm [PWR263S-20-3R30J]	3.3 uF [C1206C335K8PACTU]	3.3 uF [MDC10335K50A52P3TUBE]	3.3 uF [T491B335M020AT]
3.3 Ohm [PWR263S-20-3R30JE]	3.3 uF [C1206C335K8RACTU]	3.3 uF [MDC15335K100B53P3TUBE]	3.3 uF [T491B335M025AT]
3.3 Ohm [PWR263S-35-3R30F]	3.3 uF [C1206C335K9PACTU]	3.3 uF [MDC15335K50B53P3TUBE]	3.3 uF [T491C335M025AT]
3.3 Ohm [PWR263S-35-3R30J]	3.3 uF [C1206C335K9RACTU]	3.3 uF [MDK10335K50A52P3TUBE]	3.3 uF [T491C335M035AT]
3.3 uF [06126D335KAT2A]	3.3 uF [C1206C335M4VAC TU]	3.3 uF [MDS10335K50A52P3TUBE]	3.3 uF [T491D335M035AT]]
3.3 uF [C0805C335K4PACTU]	3.3 uF [C1206C335M9VAC TU]	3.3 uF [T409B335M006AH 4250]	3.3 uF [T491D335M050AT]]
3.3 uF [C0805C335K8PACTU]	3.3 uF [C1210C335K3PACTU]	3.3 uF [T489A335M020ATE3K7]	3.3 uF [T491S335M010AT]
3.3 uF [C0805C335K9PACTU]	3.3 uF [C1210C335K4PACTU]	3.3 uF [T491A335M004AT]	3.3 uF [T493A335M004AH 6110]
3.3 uF [C1206C335K3PACTU]	3.3 uF [C1210C335K4RACTU]	3.3 uF [T491A335M006AT]	3.3 uF [T494A335M004AT]
3.3 uF [C1206C335K4PACTU]	3.3 uF [C1210C335K8PACTU]	3.3 uF [T491A335M016AT]	3.3 uF [T494A335M006AT]
3.3 uF [C1206C335K4RACTU]	3.3 uF [MDC10335K100A52P3TUBE]	3.3 uF [T491A335M020AT]	3.3 uF [T494A335M010AT]
		3.3 uF [T491B335M016AT]	

Multisim 14.1 Education Components

3.3 uF [T494A335M020AT]	3.3 uF [T495C335M035AT E550]	3.3 uF [TAJA335K025RNJ]	3.3 uF [TAJS335K010RNJ]
3.3 uF [T494B335M016AT]	3.3 uF [T495C335M035AT E600]	3.3 uF [TAJB335K016RNJ]	3.3 uF [TAJS335K016RNJ]
3.3 uF [T494B335M020AT]	3.3 uF [T498A335M010AT E3K6]	3.3 uF [TAJB335K020RNJ]	3.3 uF [TAJT335K010RNJ]
3.3 uF [T494B335M025AT]	3.3 uF [T498A335M016AT E3K4]	3.3 uF [TAJB335K025RNJ]	3.3 uF [TAJT335K016RNJ]
3.3 uF [T494B335M035AT]	3.3 uF [T498C335M035AT E1K7]	3.3 uF [TAJC335K025RNJ]	3.3 uF [TAJT335K020RNJ]
3.3 uF [T494C335M025AT]	3.3 uF [T498C335M035AT E1K7]	3.3 uF [TAJC335K035RNJ]	3.3 uF [TAJT335K025RNJ]
3.3 uF [T494C335M035AT]	3.3 uF [TACL335K002RTA]]	3.3 uF [TAJC335K035RNJ]	3.3 uF [TAJY335K050RNJ]
3.3 uF [T494D335M050AT]	3.3 uF [TACL335K003RTA]	3.3 uF [TAJC335K050RNJ]	3.3 uF [THJA335K010RJN]
3.3 uF [T494S335M010AT]	3.3 uF [TACL335K006RTA]	3.3 uF [TAJD335K050RNJ]	3.3 uF [THJA335K016RJN]
3.3 uF [T494T335M020AT]	3.3 uF [TACR335K010RTA]	3.3 uF [TAJR335K004RNJ]	3.3 uF [THJB335K020RJN]
3.3 uF [T495A335M016AT E3K0]	3.3 uF [TAJR335K006RNJ]	3.3 uF [TAJR335K006RNJ]	3.3 uF [THJC335K035RJN]
3.3 uF [T495B335M035AT E900]	3.3 uF [TAJA335K006RNJ]	3.3 uF [TAJR335K010RNJ]	3.3 uF [TPSA335K016R350 0]
3.3 uF [T495B335M035AT E900]	3.3 uF [TAJA335K010RNJ]	3.3 uF [TAJR335K016RNJ]	3.3 uF [TPSA335K020R250 0]
3.3 uF [T495C335M035AT E525]	3.3 uF [TAJA335K016RNJ]	3.3 uF [TAJS335K004RNJ]	3.3 uF [TPSB335K016R250 0]
	3.3 uF [TAJA335K020RNJ]	3.3 uF [TAJS335K006RNJ]	

Multisim 14.1 Education Components

3.3 uF [TPSB335K020R130 0]	3.3 uH [SDR0603- 3R3ML]	3.3 uH [SRN4026- 3R3M]	3.3 uH [SRP4020TA-3R3M]
3.3 uF [TPSB335K025R200 0]	3.3 uH [SDR0604- 3R3ML]	3.3 uH [SRN5020- 3R3M]	3.3 uH [SRP5015TA-3R3M]
3.3 uF [TPSC335K035R070 0]	3.3 uH [SDR0703- 3R3ML]	3.3 uH [SRN5040- 3R3M]	3.3 uH [SRP5030T- 3R3M]
3.3 uF [TPSC335K035R070 0]	3.3 uH [SDR0805- 3R3ML]	3.3 uH [SRN6028- 3R3M]	3.3 uH [SRP5030TA-3R3M]
3.3 uF [TPSC335K050R100 0]	3.3 uH [SDR1005- 3R3ML]	3.3 uH [SRN6045- 3R3Y]	3.3 uH [SRP6540- 3R3M]
3.3 uF [TPSD335K050R080 0]	3.3 uH [SDR1006- 3R3ML]	3.3 uH [SRN8040- 3R3Y]	3.3 uH [SRP7028A- 3R3M]
3.3 uF [TPSD335K050R080 0]	3.3 uH [SDR1307- 3R3ML]	3.3 uH [SRP1038A- 3R3M]	3.3 uH [SRP7030- 3R3FM]
3.3 uF [TPST335K010R150 0]	3.3 uH [SDR1307A- 3R3M]	3.3 uH [SRP1040- 3R3M]	3.3 uH [SRP7050TA-3R3M]
3.3 uF [TRJB335K035RRJ]	3.3 uH [SDR1806- 3R3ML]	3.3 uH [SRP1235- 3R3M]	3.3 uH [SRR0603- 3R3ML]
3.3 uH [SDE0403A- 3R3M]	3.3 uH [SDR6603- 3R3M]	3.3 uH [SRP1250- 3R3M]	3.3 uH [SRR0604- 3R3ML]
3.3 uH [SDE0604A- 3R3M]	3.3 uH [SDR7045- 3R3M]	3.3 uH [SRP1265A- 3R3M]	3.3 uH [SRR0618- 3R3ML]
3.3 uH [SDE0805A- 3R3M]	3.3 uH [SRN3010- 3R3M]	3.3 uH [SRP1270- 3R3M]	3.3 uH [SRR1005- 3R3M]
3.3 uH [SDE1006A- 3R3M]	3.3 uH [SRN3015- 3R3M]	3.3 uH [SRP1770TA-3R3M]	3.3 uH [SRR1205- 3R3ML]
3.3 uH [SDR0302- 3R3ML]	3.3 uH [SRN4012T- 3R3M]	3.3 uH [SRP4012TA-3R3M]	3.3 uH [SRR1206- 3R3ML]
3.3 uH [SDR0403- 3R3ML]	3.3 uH [SRN4018- 3R3M]	3.3 uH [SRP4020- 3R3M]	3.3 uH [SRR1210- 3R3Y]

Multisim 14.1 Education Components

3.3 uH [SRR1210A-3R3Y]	3.3 uH [SRU1028A-3R3Y]	3.32 kOhm [CAY16-3321F4LF]	3.4 kOhm [CR0603-FX-3401ELF]
3.3 uH [SRR1240-3R3Y]	3.3 uH [SRU2009-3R3Y]	3.32 kOhm [CR0402-FX-3321GLF]	3.4 kOhm [CR0805-FX-3401ELF]
3.3 uH [SRR1260-3R3Y]	3.3 uH [SRU2011-3R3Y]	3.32 kOhm [CR0603-FX-3321ELF]	3.4 kOhm [CR1206-FX-3401ELF]
3.3 uH [SRR1260A-3R3Y]	3.3 uH [SRU2013-3R3Y]	3.32 kOhm [CR0805-FX-3321ELF]	3.4 kOhm [CRT0603-BY-3401ELF]
3.3 uH [SRR1280-3R3Y]	3.3 uH [SRU3011-3R3Y]	3.32 kOhm [CR1206-FX-3321ELF]	3.4 kOhm [CRT0805-BY-3401ELF]
3.3 uH [SRR3011-3R3YL]	3.3 uH [SRU3017-3R3Y]	3.32 kOhm [CR1206-FX-3321ELF]	3.48 kOhm [CR0402-FX-3481GLF]
3.3 uH [SRR4011-3R3YL]	3.3 uH [SRU5011-3R3Y]	3.32 kOhm [CRT0402-FZ-3321GLF]	3.48 kOhm [CR0603-FX-3481ELF]
3.3 uH [SRR4018-3R3Y]	3.3 uH [SRU5016-3R3Y]	3.32 kOhm [CRT0603-BY-3321ELF]	3.48 kOhm [CR0805-FX-3481ELF]
3.3 uH [SRR4028-3R3Y]	3.3 uH [SRU5028-3R3Y]	3.32 kOhm [CRT0805-BY-3321ELF]	3.48 kOhm [CR1206-FX-3481ELF]
3.3 uH [SRR6028-3R3Y]	3.3 uH [SRU5028A-3R3Y]	3.32 kOhm [CRT1206-FZ-3321ELF]	3.48 kOhm [CRT1206-BY-3481ELF]
3.3 uH [SRR6038-3R3Y]	3.3 uH [SRU6018-3R3Y]	3.32 kOhm [CR1206-FW-3324ELF]	3.5 Ohm [PWR6327W3R50J]
3.3 uH [SRR6603-3R3ML]	3.3 uH [SRU6025-3R3Y]	3.32 Ohm [CRM1206-FX-3R32ELF]	3.5 uH [SDR1305-3R5Y]
3.3 uH [SRR7032-3R3M]	3.3 uH [SRU6025A-3R3Y]	3.4 kOhm [CR0402-FX-3401GLF]	3.5 uH [SDR7030-3R5M]
3.3 uH [SRR7045-3R3M]	3.3 uH [SRU8028-3R3Y]		
3.3 uH [SRU1028-3R3Y]	3.3 uH [SRU8028A-3R3Y]		

Multisim 14.1 Education Components

3.5 uH [SRP1205-3R3Y]	3.6 kOhm [4114R-1-362LF]	3.6 kOhm [CR1206-FX-3601ELF]	3.6 nF [C0805C362K1GACTU]
3.5 uH [SRP1206-3R3Z]	3.6 kOhm [4116R-1-362]	3.6 kOhm [CR1206-FX-3601GLF]	3.6 nF [C0805C362K1HACTU]
3.5 uH [SRR0906-3R5ML]	3.6 kOhm [4308M-102-362]	3.6 kOhm [CR1206-JW-362ELF]	3.6 nF [C0805C362K3HACTU]
3.5 uH [SRR1260-3R5Y]	3.6 kOhm [4308M-102-362LF]	3.6 kOhm [CR2512-JW-362ELF]	3.6 nF [C0805C362K5HACTU]
3.5 uH [SRR1260A-3R5Y]	3.6 kOhm [4609X-101-362LF]	3.6 kOhm [CRM1206-JW-362ELF]	3.6 nF [C0805C362K5HACTU]
3.5 uH [SRR1280-3R5Y]	3.6 kOhm [CAY10-362J4LF]	3.6 MOhm [CR0603-JW-365ELF]	3.6 nF [C1825C362KBGAC TU]
3.5 uH [SRU1038-3R5Y]	3.6 kOhm [CAY16-3601F4LF]	3.6 MOhm [CR0805-FW-3604ELF]	3.6 nF [C2220C362KBGAC TU]
3.5 uH [SRU1038A-3R5Y]	3.6 kOhm [CAY16-362J4LF]	3.6 MOhm [CR0805-JW-365ELF]	3.6 nF [C2225C362KBGAC TU]
3.5 uH [SRU5018-3R5Y]	3.6 kOhm [CR0201-FW-3601GLF]	3.6 MOhm [CR1206-JW-365ELF]	3.6 Ohm [CR0603-J/-3R6ELF]
3.57 kOhm [CR0402-FX-3571GLF]	3.6 kOhm [CR0402-FX-3601GLF]	3.6 nF [C0603C362K1HACTU]	3.6 Ohm [CR0805-J/-3R6ELF]
3.57 kOhm [CR0603-FX-3571ELF]	3.6 kOhm [CR0402-JW-362GLF]	3.6 nF [C0603C362K3HACTU]	3.6 Ohm [CR1206-J/-3R6ELF]
3.57 kOhm [CR0805-FX-3571ELF]	3.6 kOhm [CR0603-FX-3601ELF]	3.6 nF [C0603C362K5HACTU]	3.6 Ohm [CRL0603-FW-3R60ELF]
3.57 kOhm [CR1206-FX-3571ELF]	3.6 kOhm [CR0603-JW-362ELF]	3.6 nF [C0603C362K5HACTU]	3.6 Ohm [CRL0805-FW-3R60ELF]
3.6 kOhm [4114R-1-362]	3.6 kOhm [CR0805-FX-3601ELF]		
	3.6 kOhm [CR0805-JW-362ELF]		

Multisim 14.1 Education Components

3.6 Ohm [CRL0805-JW-3R60ELF]	3.65 kOhm [CR2010-FX-3651ELF]	3.8 kOhm [4308R-102-382]	3.9 kOhm [4116R-1-392LF]
3.6 Ohm [CRL1206-FW-3R60ELF]	3.65 kOhm [CRT0603-BY-3651ELF]	3.8 uH [SRU1038-3R8Y]	3.9 kOhm [4116R-2-392]
3.6 Ohm [CRL1206-JW-3R60ELF]	3.65 kOhm [CRT0603-DY-3651ELF]	3.83 kOhm [CR0402-FX-3831GLF]	3.9 kOhm [4116R-2-392LF]
3.6 Ohm [CRL2010-FW-3R60ELF]	3.65 kOhm [CRT0603-FY-3651ELF]	3.83 kOhm [CR0603-FX-3831ELF]	3.9 kOhm [4306M-101-392]
3.6 Ohm [CRL2010-JW-3R60ELF]	3.65 kOhm [CRT0805-FY-3651ELF]	3.83 kOhm [CR0805-FX-3831ELF]	3.9 kOhm [4306M-101-392LF]
3.6 Ohm [CRL2512-FW-3R60ELF]	3.74 kOhm [CR0402-FX-3741GLF]	3.83 kOhm [CR1206-FX-3831ELF]	3.9 kOhm [4306R-101-392]
3.6 Ohm [CRM0805-JW-3R6ELF]	3.74 kOhm [CR0603-FX-3741ELF]	3.83 kOhm [CRT0402-FZ-3831GLF]	3.9 kOhm [4306R-101-392LF]
3.6 Ohm [CRM2512-JW-3R6ELF]	3.74 kOhm [CR0805-FX-3741ELF]	3.83 kOhm [CR0805-FX-3834ELF]	3.9 kOhm [4306R-102-392]
3.6 uH [SRN8040-3R6Y]	3.74 kOhm [CR1206-FX-3741ELF]	3.83 MOhm [CR0805-FX-3834ELF]	3.9 kOhm [4306R-102-392LF]
3.65 kOhm [CR0402-FX-3651GLF]	3.74 kOhm [CR1206-FX-3741GLF]	3.83 MOhm [CR0805-FX-3834ELF]	3.9 kOhm [4308H-101-392]
3.65 kOhm [CR0603-FX-3651ELF]	3.74 kOhm [CRT0603-BW-3741ELF]	3.9 kOhm [4114R-1-392]	3.9 kOhm [4308H-102-392]
3.65 kOhm [CR0805-FX-3651ELF]	3.74 kOhm [CRT0603-DX-3741ELF]	3.9 kOhm [4114R-1-392LF]	3.9 kOhm [4308M-101-392]
3.65 kOhm [CR1206-FX-3651ELF]		3.9 kOhm [4114R-2-392]	3.9 kOhm [4308M-101-392LF]
		3.9 kOhm [4114R-2-392LF]	3.9 kOhm [4308M-102-392]
		3.9 kOhm [4116R-1-392]	3.9 kOhm [4308M-102-392LF]

Multisim 14.1 Education Components

3.9 kOhm [4308R-101-392]	3.9 kOhm [4420P-T02-392]	3.9 kOhm [4610H-101-392LF]	3.9 kOhm [CAT16-3901F4LF]
3.9 kOhm [4308R-101-392LF]	3.9 kOhm [4604X-101-392LF]	3.9 kOhm [4610H-102-392LF]	3.9 kOhm [CAT16-392J4LF]
3.9 kOhm [4308R-102-392]	3.9 kOhm [4604X-102-392LF]	3.9 kOhm [4610X-101-392LF]	3.9 kOhm [CAT16-392J8LF]
3.9 kOhm [4308R-102-392LF]	3.9 kOhm [4605X-101-392LF]	3.9 kOhm [4610X-102-392LF]	3.9 kOhm [CAT25-392JALF]
3.9 kOhm [4309R-101-392]	3.9 kOhm [4606H-102-392LF]	3.9 kOhm [4612X-102-392LF]	3.9 kOhm [CAY10-392J4LF]
3.9 kOhm [4309R-101-392LF]	3.9 kOhm [4606X-101-392LF]	3.9 kOhm [4816P-1-392]	3.9 kOhm [CAY16-3901F4LF]
3.9 kOhm [4310M-101-392]	3.9 kOhm [4606X-102-392LF]	3.9 kOhm [4816P-1-392LF]	3.9 kOhm [CAY16-392J4LF]
3.9 kOhm [4310M-101-392LF]	3.9 kOhm [4606X-AP1-392LF]	3.9 kOhm [4816P-2-392]	3.9 kOhm [CAY16-392J8LF]
3.9 kOhm [4310M-102-392]	3.9 kOhm [4606X-AP2-392LF]	3.9 kOhm [4816P-2-392LF]	3.9 kOhm [CR0402-FX-3901GLF]
3.9 kOhm [4310R-101-392]	3.9 kOhm [4607X-101-392LF]	3.9 kOhm [4816P-T01-392]	3.9 kOhm [CR0402-JW-392GLF]
3.9 kOhm [4310R-101-392LF]	3.9 kOhm [4608H-102-392LF]	3.9 kOhm [4816P-T01-392LF]	3.9 kOhm [CR0603-FX-3901ELF]
3.9 kOhm [4310R-102-392]	3.9 kOhm [4608X-101-392LF]	3.9 kOhm [4816P-T02-392]	3.9 kOhm [CR0603-JW-392ELF]
3.9 kOhm [4310R-102-392LF]	3.9 kOhm [4608X-102-392LF]	3.9 kOhm [4816P-T02-392LF]	3.9 kOhm [CR0603-JW-392GLF]
3.9 kOhm [4420P-2-392]	3.9 kOhm [4609H-101-392LF]	3.9 kOhm [4820P-2-392]	3.9 kOhm [CR0805-FX-3901ELF]
3.9 kOhm [4420P-T01-392]	3.9 kOhm [4609X-101-392LF]	3.9 kOhm [4820P-T02-392]	3.9 kOhm [CR0805-JW-392ELF]

Multisim 14.1 Education Components

3.9 kOhm [CR1206-FX-3901ELF]	3.9 MOhm [CR0603-FX-3904ELF]	3.9 nF [C0603C392K3RACT U]	3.9 nF [C0805C392K4GACT U]
3.9 kOhm [CR1206-JW-392ELF]	3.9 MOhm [CR0603-JW-395ELF]	3.9 nF [C0603C392K4RACT U]	3.9 nF [C0805C392K4RACT U]
3.9 kOhm [CR2010-JW-392ELF]	3.9 MOhm [CR0805-JW-395ELF]	3.9 nF [C0603C392K5HACT U]	3.9 nF [C0805C392K5GACT U]
3.9 kOhm [CRM1206-JW-392ELF]	3.9 MOhm [CR1206-JW-395ELF]	3.9 nF [C0603C392K5RACT U]	3.9 nF [C0805C392K5HACT U]
3.9 kOhm [CRT1206-AV-3901ELF]	3.9 nF [C0402C392K3RACT U]	3.9 nF [C0805C392K1GACT U]	3.9 nF [C0805C392K5RACT U]
3.9 mH [SDR0503-392JL]	3.9 nF [C0402C392K4RACT U]	3.9 nF [C0805C392K1HACT U]	3.9 nF [C0805C392KARACT U]
3.9 mH [SDR0805-392KL]	3.9 nF [C0402C392K5RACT U]	3.9 nF [C0805C392K1RACT U]	3.9 nF [C1206C392K1GACT U]
3.9 mH [SDR0906-392KL]	3.9 nF [C0603C392K1HACT U]	3.9 nF [C0805C392K2RACT U]	3.9 nF [C1206C392K1RACT U]
3.9 mH [SRR0906-392YL]	3.9 nF [C0603C392K1RACT U]	3.9 nF [C0805C392K3GACT U]	3.9 nF [C1206C392K2RACT U]
3.9 mH [SRR1208-392KL]	3.9 nF [C0603C392K3GACT U]	3.9 nF [C0805C392K3HACT U]	3.9 nF [C1206C392K5GACT U]
3.9 MOhm [CAT25-395JALF]	3.9 nF [C0603C392K3HACT U]	3.9 nF [C0805C392K3RACT U]	3.9 nF [C1206C392K5RACT U]

Multisim 14.1 Education Components

3.9 nF [C1210C392K5RACT U]	3.9 nF [GMC7.3392K400K3 1TR12]	3.9 Ohm [CR0402- J/-3R9GLF]	3.9 Ohm [CRM2512-JW- 3R9ELF]
3.9 nF [C1812C392K2GACT U]	3.9 nF [GMC7.3393K100K3 1TR12]	3.9 Ohm [CR0603- J/-3R9ELF]	3.9 Ohm [PWR263S-35- 3R90FE]
3.9 nF [C1825C392KBGAC TU]	3.9 nF [GMC7.3393K250K3 7TR12]	3.9 Ohm [CR0805- J/-3R9ELF]	3.9 Ohm [PWR4318W3R90JE]
3.9 nF [C2220C392KBGAC TU]	3.9 nF [MMC5.7392K100J 31TR12]	3.9 Ohm [CR1206- J/-3R9ELF]	3.9 Ohm [PWR5322W3R90JE]
3.9 nF [C2225C392KBGAC TU]	3.9 nF [MMC5.7392K250J 31TR12]	3.9 Ohm [CR2010- J/-3R9ELF]	3.9 uF [35TQC3R9MYF]
3.9 nF [C2225C392KCGAC TU]	3.9 nF [MMC5.7392K50J3 1TR12]	3.9 Ohm [CRL0603- JW-3R90ELF]	3.9 uF [C1206C395K4RACT U]
3.9 nF [CDR02BX392BKSM]	3.9 nF [MMC7.3392K100K 31TR12]	3.9 Ohm [CRL0805- FW-3R90ELF]	3.9 uF [C1206C395K8RACT U]
3.9 nF [GMC5.7392K100J3 1TR12]	3.9 nF [MMC7.3392K250K 31TR12]	3.9 Ohm [CRL0805- JW-3R90ELF]	3.9 uF [C1206C395K9RACT U]
3.9 nF [GMC5.7392K50J31 TR12]	3.9 nF [MMC7.3392K400K 31TR12]	3.9 Ohm [CRL1206- JW-3R90ELF]	3.9 uF [C1210C395K3NAC TU]
3.9 nF [GMC5.7393K100J3 5TR12]	3.9 nF [MMC7.3392K50K3 1TR12]	3.9 Ohm [CRL2010- FW-3R90ELF]	3.9 uF [MDC10395K100A5 2P3TUBE]
3.9 nF [GMC7.3392K100K3 1TR12]	3.9 nF [MMC7.3392K63K3 1TR12]	3.9 Ohm [CRL2512- FW-3R90ELF]	3.9 uF [MDC10395K50A52 P3TUBE]
		3.9 Ohm [CRM2512-FX- 3R90ELF]	

Multisim 14.1 Education Components

3.9 uF [MDC15395K100B5 3P3TUBE]	3.9 uH [SDR0805- 3R9ML]	3.92 kOhm [CR0402-FX- 3921GLF]	30 kOhm [4304M- 101-303]
3.9 uF [MDC15395K50B53 P3TUBE]	3.9 uH [SDR0906- 3R9ML]	3.92 kOhm [CR0603-FX- 3921ELF]	30 kOhm [4306M- 102-303]
3.9 uF [MDK15395K100B5 3P3TUBE]	3.9 uH [SDR1006- 3R9ML]	3.92 kOhm [CR0805-FX- 3921ELF]	30 kOhm [4308R- 102-303]
3.9 uF [MDS15395K100B5 3P3TUBE]	3.9 uH [SRN6028- 3R9M]	3.92 kOhm [CR0805-FX- 3921ELF]	30 kOhm [4308R- 102-303LF]
3.9 uF [MDS15395K100B5 3P3TUBE]	3.9 uH [SRP1040- 3R9M]	3.92 kOhm [CR1206-FX- 3921ELF]	30 kOhm [4310R- 101-303]
3.9 uF [MDS15395K50B53 P3TUBE]	3.9 uH [SRR0805- 3R9M]	3.92 kOhm [CRM1206-FX- 3921ELF]	30 kOhm [4310R- 101-303LF]
3.9 uF [MMC12.7395K50B 31TR24]	3.9 uH [SRR1003- 3R9M]	3.92 kOhm [CRT0603-BY- 3921ELF]	30 kOhm [4605X- 101-303LF]
3.9 uH [SDE0604A- 3R9M]	3.9 uH [SRR1240- 3R9Y]	3.92 kOhm [CRT1206-BY- 3921ELF]	30 kOhm [4608X- 102-303LF]
3.9 uH [SDE1006A- 3R9M]	3.9 uH [SRR4018- 3R9Y]	3.92 Ohm [CRM1206-FX- 3R92ELF]	30 kOhm [4609X- 101-303LF]
3.9 uH [SDR0302- 3R9ML]	3.9 uH [SRR4028- 3R9Y]	30 kOhm [4814P-2- 303]	
3.9 uH [SDR0403- 3R9ML]	3.9 uH [SRR5018- 3R9Y]	30 kOhm [4814P-2- 303LF]	
3.9 uH [SDR0603- 3R9ML]	3.9 uH [SRR6028- 3R9Y]	30 GOhm [4116R- 1-309G]	30 kOhm [4816P-1- 303F]
3.9 uH [SDR0604- 3R9ML]	3.9 uH [SRR7045- 3R9M]	30 GOhm [4116R- 1-309GLF]	30 kOhm [CAT16- 303J4LF]
3.9 uH [SDR0703- 3R9ML]	3.9 uH [SRU8043- 3R9Y]	30 kOhm [4116R-1- 303]	30 kOhm [CAY16- 303J4LF]
		30 kOhm [4116R-1- 303LF]	

Multisim 14.1 Education Components

30 kOhm [CR0201-FW-3002GLF]	30 kOhm [CRT0805-BY-3002ELF]	30 mF [C0402C309K5GACTU]	30 mOhm [PWR163S-25-R030JE]
30 kOhm [CR0402-FX-3002GLF]	30 kOhm [CRT0805-FV-3002ELF]	30 mF [C0805C309KBGACTU]	30 mOhm [PWR1913WR030F]
30 kOhm [CR0603-FX-3002ELF]	30 kOhm [CRT1206-BY-3002ELF]	30 mOhm [CRA2512-FZ-R030ELF]	30 mOhm [PWR1913WR030F E]
30 kOhm [CR0603-JW-303ELF]	30 kOhm [PWR163S-25-3002J]	30 mOhm [CRA2512-JZ-R030ELF]	30 mOhm [PWR1913WR030J]
30 kOhm [CR0805-FX-3002ELF]	30 kOhm [PWR220T-20-3002F]	30 mOhm [CRF2512-FZ-R030ELF]	30 mOhm [PWR1913WR030JE]]
30 kOhm [CR0805-JW-303ELF]	30 kOhm [PWR220T-20-3002J]	30 mOhm [CRF2512-JZ-R030ELF]	30 mOhm [PWR221T-30-R030J]
30 kOhm [CR1206-FX-3002ELF]	30 kOhm [PWR221T-30-3002F]	30 mOhm [CRL1206-FV-R030ELF]	30 mOhm [PWR2615WR030F]
30 kOhm [CR1206-JW-303ELF]	30 kOhm [PWR263S-20-3002F]	30 mOhm [CRL1206-JV-R030ELF]	30 mOhm [PWR2615WR030F E]
30 kOhm [CR2010-FX-3002ELF]	30 kOhm [PWR263S-20-3002J]	30 mOhm [CRL2010-FV-R030ELF]	30 mOhm [PWR2615WR030J]
30 kOhm [CR2010-JW-303ELF]	30 kOhm [PWR263S-35-3002F]	30 mOhm [CRL2010-JV-R030ELF]	30 mOhm [PWR4412-2SBR0300F]
30 kOhm [CRM2512-FX-3002ELF]	30 kOhm [PWR263S-35-3002J]	30 mOhm [CRL2512-FV-R030ELF]	30 mOhm [PWR4412-2SBR0300J]
30 kOhm [CRM2512-JW-303ELF]			
30 kOhm [CRT0402-BY-3002GLF]			
30 kOhm [CRT0603-BY-3002ELF]			

Multisim 14.1 Education Components

30 mOhm [PWR4412- 2SCR0300F]	30 Ohm [4816P- T01-300]	30 Ohm [CR0805- JW-300ELF]	30 Ohm [PWR220T-35- 30R0J]
30 mOhm [PWR4412- 2SCR0300J]	30 Ohm [4816P- T01-300LF]	30 Ohm [CR1206- FX-30R0ELF]	30 Ohm [PWR221T-30- 30R0J]
30 mOhm [PWR4412- 2SDR0300F]	30 Ohm [CAT10- 300J4LF]	30 Ohm [CR1206- JW-300ELF]	30 Ohm [PWR263S-20- 30R0F]
30 mOhm [PWR4412- 2SDR0300J]	30 Ohm [CAT16- 30R0F4LF]	30 Ohm [CRM2512-JW- 300ELF]	30 Ohm [PWR263S-20- 30R0J]
30 mOhm [PWR4525WR030J]	30 Ohm [CAY10- 300J2LF]	30 Ohm [CRT0805- FX-30R0ELF]	30 Ohm [PWR263S-35- 30R0F]
30 mOhm [PWR4525WR030JE]	30 Ohm [CAY10- 300J4LF]	30 Ohm [PWR163S-25- 30R0F]	30 Ohm [PWR263S-35- 30R0J]
30 mOhm [PWR6327WR030J]	30 Ohm [CAY16- 300J8LF]	30 Ohm [PWR163S-25- 30R0FE]	30 Ohm [PWR6327W30R0J]
30 mOhm [PWR6327WR030JE]	30 Ohm [CR0402- FX-30R0GLF]	30 Ohm [PWR163S-25- 30R0J]	30 pF [C0402C300K5GACT U]
30 Ohm [4116R-1- 300]	30 Ohm [CR0402- JW-300GLF]	30 Ohm [PWR163S-25- 30R0JE]	30 pF [C0603C300K2GACT U]
30 Ohm [4310M- 102-300]	30 Ohm [CR0603- FX-30R0ELF]	30 Ohm [PWR220T-20- 30R0F]	30 pF [C0603C300K5GACT U]
30 Ohm [4310M- 102-300LF]	30 Ohm [CR0603- JW-300ELF]	30 Ohm [PWR220T-20- 30R0J]	30 pF [C0805C300K2GACT U]
30 Ohm [4310R- 102-300LF]	30 Ohm [CR0805- FX-30R0ELF]		
30 Ohm [4608X- 102-300LF]	30 Ohm [CR0805- FX-30R0GLF]		

Multisim 14.1 Education Components

30 pF [C0805C300K5GACT U]	30.1 kOhm [CR0201-FW- 3012GLF]	30.1 Ohm [CAT16- 30R1F4LF]	30.9 kOhm [CR0805-FX- 3092ELF]
30 pF [C0805C300KBGAC TU]	30.1 kOhm [CR0402-FX- 3012GLF]	30.1 Ohm [CAY16- 30R1F4LF]	30.9 kOhm [CR1206-FX- 3092ELF]
30 pF [C1206C300K1GACT U]	30.1 kOhm [CR0603-FX- 3012ELF]	30.1 Ohm [CR0603- FX-30R1ELF]	30.9 kOhm [CRM2512-FX- 3092ELF]
30 pF [C1206C300K5GACT U]	30.1 kOhm [CR0805-FX- 3012ELF]	30.1 Ohm [CR0805- FX-30R1ELF]	30.9 kOhm [CRT0603-BY- 3092ELF]
30 pF [C1206C300KBGAC TU]	30.1 kOhm [CR1206-FX- 3012ELF]	30.1 Ohm [CR1206- FX-30R1ELF]	30.9 Ohm [CR0402- FX-30R9GLF]
30 pF [C1210C300KBGAC TU]	30.1 kOhm [CRM2512-FX- 3012ELF]	30.1 Ohm [CR2010- FX-30R1ELF]	30.9 Ohm [CR0603- FX-30R9ELF]
30 pF [C1812C300KBGAC TU]	30.1 kOhm [CRM1206-FX- 30R1ELF]	30.1 Ohm [CRM1206-FX- 30R1ELF]	30.9 Ohm [CR0805- FX-30R9ELF]
30 pF [C1825C300KBGAC TU]	30.1 kOhm [CR1206-FX- 3012ELF]	30.1 Ohm [CR2010- FX-30R1ELF]	30.9 Ohm [CR1206- FX-30R9ELF]
30 pF [C2220C300KBGAC TU]	30.1 kOhm [CRM2512-FX- 3012ELF]	30.1 Ohm [CRM1206-FX- 30R1ELF]	30 AMP
30 pF [C2225C300KBGAC TU]	30.1 kOhm [CRM1206-FX- 30R1ELF]	30.1 Ohm [CRM1206-FX- 30R1ELF]	300 kOhm [4116R- 1-304LF]
30.1 kOhm [CAT16- 3012F4LF]	30.1 kOhm [CRM1206-FX- 30R1ELF]	30.1 Ohm [CRM1206-FX- 30R1ELF]	300 kOhm [4116R- 2-304]
30.1 kOhm [CAY16- 3012F4LF]	30.1 kOhm [CRM1206-FX- 30R1ELF]	30.1 Ohm [CRM1206-FX- 30R1ELF]	300 kOhm [4116R- 2-304LF]
	30.1 kOhm [CRM1206-FX- 30R1ELF]	30.1 Ohm [CRM1206-FX- 30R1ELF]	300 kOhm [4605X- 101-304LF]
	30.1 kOhm [CRM1206-FX- 30R1ELF]	30.1 Ohm [CRM1206-FX- 30R1ELF]	300 kOhm [CAY16- 304J4LF]

Multisim 14.1 Education Components

300 kOhm [CR0201-FW-3003GLF]	300 mOhm [CRL0603-FW-R300ELF]	300 mOhm [CRM2512-FX-R300ELF]	300 mOhm [PWR4525WR300JE]
300 kOhm [CR0402-FX-3003GLF]	300 mOhm [CRL0603-JW-R300ELF]	300 mOhm [CRM2512-JX-R300ELF]	300 mOhm [PWR6327WR300J]
300 kOhm [CR0402-JW-304GLF]	300 mOhm [CRL0805-FW-R300ELF]	300 mOhm [PWR163S-25-R300FE]	300 mOhm [PWR6327WR300JE]
300 kOhm [CR0603-FX-3003ELF]	300 mOhm [CRL0805-JW-R300ELF]	300 mOhm [PWR1913WR300J]	300 Ohm [4114R-1-301]
300 kOhm [CR0603-JW-304ELF]	300 mOhm [CRL1206-FW-R300ELF]	300 mOhm [PWR1913WR300JE]	300 Ohm [4114R-2-301]
300 kOhm [CR0805-FX-3003ELF]	300 mOhm [CRL1206-JW-R300ELF]	300 mOhm [PWR220T-20-R300J]	300 Ohm [4116R-1-301LF]
300 kOhm [CR0805-JW-304ELF]	300 mOhm [CRL2010-FW-R300ELF]	300 mOhm [PWR221T-30-R300F]	300 Ohm [4116R-2-301]
300 kOhm [CR1206-FX-3003ELF]	300 mOhm [CRL2010-JW-R300ELF]	300 mOhm [PWR221T-30-R300J]	300 Ohm [4116R-2-301LF]
300 kOhm [CR1206-JW-304ELF]	300 mOhm [CRL2512-FW-R300ELF]	300 mOhm [PWR2615WR300J]	300 Ohm [4306M-102-301]
300 kOhm [CRS1206-FX-3003ELF]	300 mOhm [CRL2512-JW-R300ELF]	300 mOhm [PWR2615WR300JE]	300 Ohm [4306M-102-301LF]
300 kOhm [CRT0603-BY-3003ELF]	300 mOhm [CRM2010-FX-R300ELF]	300 mOhm [PWR263S-35-R300F]	300 Ohm [4306R-101-301]
		300 mOhm [PWR4525WR300J]	300 Ohm [4306R-101-301LF]
			300 Ohm [4308R-101-301]
			300 Ohm [4308R-102-301]

Multisim 14.1 Education Components

300 Ohm [4308R-102-301LF]	300 Ohm [CR0402-JW-301GLF]	300 Ohm [PWR163S-25-3000FE]	300 pF [C1206C301K5GACT U]
300 Ohm [4310R-101-301]	300 Ohm [CR0603-FX-3000ELF]	300 Ohm [PWR221T-30-3000F]	300 pF [C1206C301KBGAC TU]
300 Ohm [4310R-101-301LF]	300 Ohm [CR0603-JW-301ELF]	300 Ohm [PWR263S-35-3000F]	300 pF [C1210C301KBGAC TU]
300 Ohm [4606X-102-301LF]	300 Ohm [CR0805-FX-3000ELF]	300 Ohm [PWR263S-35-3000FE]	300 pF [C1812C301KBGAC TU]
300 Ohm [4608X-102-301LF]	300 Ohm [CR0805-JW-301ELF]	300 Ohm [PWR263S-35-3000FE]	300 pF [C1825C301KBGAC TU]
300 Ohm [4610X-101-301LF]	300 Ohm [CR1206-FX-3000ELF]	300 Ohm [PWR263S-35-3000J]	300 pF [C2220C301KBGAC TU]
300 Ohm [4816P-1-301]	300 Ohm [CR1206-JW-301ELF]	300 pF [C0402C301K1HACT U]	300 pF [C2225C301KBGAC TU]
300 Ohm [4816P-T02-301]	300 Ohm [CR2010-FX-3000ELF]	300 pF [C0402C301K3HACT U]	301 kOhm [CR0402-FX-3013GLF]
300 Ohm [CAT16-301J4LF]	300 Ohm [CR2010-JW-301ELF]	300 pF [C0805C301K1GACT U]	301 kOhm [CR0603-FX-3013ELF]
300 Ohm [CAT25-301JALF]	300 Ohm [CR2512-JW-301ELF]	300 pF [C0805C301K2GACT U]	301 kOhm [CR0805-FX-3013ELF]
300 Ohm [CAY10-301J4LF]	300 Ohm [CRT0402-FZ-3000GLF]	300 pF [C0805C301K5GACT U]	
300 Ohm [CAY16-3000F4LF]	300 Ohm [CRT0603-BZ-3000ELF]		
300 Ohm [CAY16-301J4LF]	300 Ohm [CRT0805-FX-3000ELF]		
300 Ohm [CR0201-JW-301GLF]	300 Ohm [CRT1206-BY-3000ELF]		
300 Ohm [CR0402-FX-3000GLF]			

Multisim 14.1 Education Components

301 Ohm [CAY16-3010F4LF]	309 kOhm [CR0805-FX-3093ELF]	31.6 kOhm [CR0402-FX-3162GLF]	316 kOhm [CR0805-FX-3163ELF]
301 Ohm [CR0402-FX-3010GLF]	309 kOhm [CR1206-FX-3093ELF]	31.6 kOhm [CR0603-FX-3162ELF]	316 kOhm [CR1206-FX-3163ELF]
301 Ohm [CR0603-FX-3010ELF]	309 Ohm [CR0402-FX-3090GLF]	31.6 kOhm [CR0805-FX-3162ELF]	316 Ohm [CR0402-FX-3160GLF]
301 Ohm [CR0805-FX-3010ELF]	309 Ohm [CR0603-FX-3090ELF]	31.6 kOhm [CR1206-FX-3162ELF]	316 Ohm [CR0603-FX-3160ELF]
301 Ohm [CR1206-FX-3010ELF]	309 Ohm [CR0805-FX-3090ELF]	31.6 kOhm [CRT0402-FZ-3162GLF]	316 Ohm [CR0805-FX-3160ELF]
301 Ohm [CR2512-FX-3010ELF]	309 Ohm [CR1206-FX-3090ELF]	31.6 kOhm [CR0402-FX-31R6GLF]	316 Ohm [CRT0402-FZ-3160GLF]
301 Ohm [CRM1206-FX-3010ELF]	30CLJQ045	31.6 Ohm [CR0603-FX-31R6ELF]	32 kOhm [4609M-101-323LF]
301 Ohm [CRT0402-FZ-3010GLF]	30CLJQ100	31.6 Ohm [CR0805-FX-31R6ELF]	32.4 kOhm [CR0402-FX-3242GLF]
301 Ohm [CRT0603-BV-3010ELF]	30CLJQ150	31.6 Ohm [CR1206-FX-31R6ELF]	32.4 kOhm [CR0603-FX-3242ELF]
301 Ohm [CRT0603-BX-3010ELF]	30LJQ045	31.6 Ohm [CRT0402-FZ-31R6GLF]	32.4 kOhm [CR0805-FX-3242ELF]
301 Ohm [CRT0603-BY-3010ELF]	30LJQ100	316 kOhm [CR0402-FX-3163GLF]	32.4 kOhm [CR1206-FX-3242ELF]
301 Ohm [CRT0603-BZ-3010ELF]	30LJQ150	316 kOhm [CR0603-FX-3163ELF]	
301 Ohm [CRT0603-CX-3010ELF]	30SCLJQ030		
301 Ohm [CRT0603-CY-3010ELF]	30SCLJQ060		
301 Ohm [CRT0603-DX-3010ELF]	30SLJQ030		
301 Ohm [CRT0603-DY-3010ELF]	30V_10W		
309 kOhm [CR0402-FX-3093GLF]	31.2 kOhm [CR1206-FX-3122ELF]		
309 kOhm [CR0603-FX-3093ELF]	31.6 kOhm [CR0201-FW-3162GLF]		

Multisim 14.1 Education Components

32.4 kOhm [CRT0603-BY- 3242ELF]	324 Ohm [CR0402- FX-3240GLF]	33 kOhm [4116R-2- 333LF]	33 kOhm [4309R- 101-333]
32.4 kOhm [CRT0805-FY- 3242ELF]	324 Ohm [CR0603- FX-3240ELF]	33 kOhm [4306H- 101-333]	33 kOhm [4309R- 101-333LF]
32.4 Ohm [CR0402- FX-32R4GLF]	324 Ohm [CR0805- FX-3240ELF]	33 kOhm [4306H- 101-333LF]	33 kOhm [4310H- 101-333]
32.4 Ohm [CR0603- FX-32R4ELF]	324 Ohm [CR1206- FX-3240ELF]	33 kOhm [4306R- 101-333]	33 kOhm [4310H- 101-333LF]
32.4 Ohm [CR0805- FX-32R4ELF]	324 Ohm [CRT0805-BV- 3240ELF]	33 kOhm [4306R- 101-333LF]	33 kOhm [4310R- 101-333]
32.4 Ohm [CR1206- FX-32R4ELF]	324 Ohm [CRT0805-BY- 3240ELF]	33 kOhm [4306R- 102-333]	33 kOhm [4310R- 101-333LF]
32.4 Ohm [PWR6327W32R4F]	3280A	33 kOhm [4306R- 102-333LF]	33 kOhm [4310R- 102-333]
32.8 kOhm [CR1206-FX- 3282ELF]	3288RT	33 kOhm [4308M- 101-333]	33 kOhm [4310R- 102-333LF]
320 nH [SRP1270- R32M]	32CTQ030	33 kOhm [4308M- 101-333LF]	33 kOhm [4416P-1- 333LF]
324 kOhm [CR0402-FX- 3243GLF]	33 kOhm [4114R-1- 333]	33 kOhm [4308M- 102-333]	33 kOhm [4416P-2- 333]
324 kOhm [CR0603-FX- 3243ELF]	33 kOhm [4114R-1- 333LF]	33 kOhm [4308M- 102-333LF]	33 kOhm [4420P-2- 333]
324 kOhm [CR0805-FX- 3243ELF]	33 kOhm [4114R-2- 333]	33 kOhm [4308M- 102-333LF]	33 kOhm [4420P- T01-333]
324 kOhm [CR1206-FX- 3243ELF]	33 kOhm [4114R-2- 333LF]	33 kOhm [4308R- 101-333]	33 kOhm [4420P- T02-333]
	33 kOhm [4116R-1- 333]	33 kOhm [4308R- 101-333LF]	33 kOhm [4604X- 101-333LF]
	33 kOhm [4116R-1- 333LF]	33 kOhm [4308R- 102-333]	33 kOhm [4604X- 101-333LF]
	33 kOhm [4116R-2- 333]	33 kOhm [4308R- 102-333LF]	33 kOhm [4604X- 102-333LF]

Multisim 14.1 Education Components

33 kOhm [4605X-101-333LF]	33 kOhm [4610X-102-333LF]	33 kOhm [4816P-2-333LF]	33 kOhm [CAT16-333J8LF]
33 kOhm [4606H-101-333LF]	33 kOhm [4610X-AP1-333LF]	33 kOhm [4816P-T01-333]	33 kOhm [CAT25-333JALF]
33 kOhm [4606M-102-333LF]	33 kOhm [4611X-101-333LF]	33 kOhm [4816P-T01-333LF]	33 kOhm [CAY10-333J4LF]
33 kOhm [4606X-101-333LF]	33 kOhm [4613X-101-333LF]	33 kOhm [4816P-T02-333]	33 kOhm [CAY16-3302F4LF]
33 kOhm [4606X-102-333LF]	33 kOhm [4614X-102-333LF]	33 kOhm [4816P-T02-333LF]	33 kOhm [CAY16-333J4LF]
33 kOhm [4606X-AP1-333LF]	33 kOhm [4814P-1-333]	33 kOhm [4818P-T02-333]	33 kOhm [CAY16-333J8LF]
33 kOhm [4606X-AP2-333LF]	33 kOhm [4814P-1-333LF]	33 kOhm [4820P-1-333]	33 kOhm [CAY17-333JALF]
33 kOhm [4607X-101-333LF]	33 kOhm [4814P-2-333]	33 kOhm [4820P-1-333LF]	33 kOhm [CR0201-FW-3302GLF]
33 kOhm [4608X-101-333LF]	33 kOhm [4814P-2-333LF]	33 kOhm [4820P-2-333]	33 kOhm [CR0402-FX-3302GLF]
33 kOhm [4608X-102-333LF]	33 kOhm [4814P-T01-333]	33 kOhm [4820P-T01-333]	33 kOhm [CR0402-JW-333GLF]
33 kOhm [4608X-AP1-333LF]	33 kOhm [4814P-T02-333]	33 kOhm [4820P-T01-333LF]	33 kOhm [CR0603-FX-3302ELF]
33 kOhm [4609M-101-333LF]	33 kOhm [4814P-T02-333LF]	33 kOhm [4820P-T02-333]	33 kOhm [CR0603-JW-333ELF]
33 kOhm [4609X-101-333LF]	33 kOhm [4816P-1-333]	33 kOhm [CAT10-333J4LF]	33 kOhm [CR0603-JW-333GLF]
33 kOhm [4610M-101-333LF]	33 kOhm [4816P-1-333LF]	33 kOhm [CAT16-3302F4LF]	33 kOhm [CR0805-FX-3302ELF]
33 kOhm [4610X-101-333LF]	33 kOhm [4816P-2-333]	33 kOhm [CAT16-333J4LF]	33 kOhm [CR0805-JW-333ELF]

Multisim 14.1 Education Components

33 kOhm [CR0805-JW-333GLF]	33 mOhm [CRF2512-FZ-R033ELF]	33 nF [C0402C333K4RACTU]	33 nF [C0805C333K1RACTU]
33 kOhm [CR1206-FX-3302ELF]	33 mOhm [CRF2512-JZ-R033ELF]	33 nF [C0402C333K8PACTU]	33 nF [C0805C333K2RACTU]
33 kOhm [CR1206-JW-333ELF]	33 mOhm [CRL2512-JV-R033ELF]	33 nF [C0402C333K8RACTU]	33 nF [C0805C333K3GACTU]
33 kOhm [CRM1206-JW-333ELF]	33 mOhm [PWR163S-25-R033J]	33 nF [C0402C333K9PACTU]	33 nF [C0805C333K3HACTU]
33 kOhm [CRM2512-FX-3302ELF]	33 mOhm [PWR163S-25-R033JE]	33 nF [C0402C333K9RACTU]	33 nF [C0805C333K3RACTU]
33 kOhm [CRM2512-JW-333ELF]	33 mOhm [PWR1913WR033F]	33 nF [C0603C333K1RACTU]	33 nF [C0805C333K4RACTU]
33 kOhm [CRT0402-CZ-3302GLF]	33 mOhm [PWR1913WR033FE]	33 nF [C0603C333K3RACTU]	33 nF [C0805C333K5RACTU]
33 kOhm [CRT0603-BY-3302ELF]	33 mOhm [PWR220T-20-R033J]	33 nF [C0603C333K4RACTU]	33 nF [C0805C333K8RACTU]
33 kOhm [PWR220T-20-3302F]	33 mOhm [PWR221T-30-R033J]	33 nF [C0603C333K5RACTU]	33 nF [C0805C333M5UAC TU]
33 mF [C0805C339KBGAC TU]	33 mOhm [PWR2615WR033F]	33 nF [C0603C333K8RACTU]	33 nF [C0805F333K1RACTU]
33 mF [C1206C339K5GACTU]	33 mOhm [PWR2615WR033FE]	33 nF [C0603C333M3VAC TU]	33 nF [C0805F333K3RACTU]
	33 nF [C0402C333K3RACTU]		

Multisim 14.1 Education Components

33 nF [C0805F333K4RACT U]	33 nF [C1206C333M5UAC TU]	33 nF [C1812C333K1GACT U]	33 nF [C2220C333K5GACT U]
33 nF [C0805F333K5RACT U]	33 nF [C1210C333K1GACT U]	33 nF [C1812C333K1HACT U]	33 nF [C2225C333K5GACT U]
33 nF [C1206C333K1HACT U]	33 nF [C1210C333K1HACT U]	33 nF [C1812C333K1RACT U]	33 nF [CA064C333K4RACT U]
33 nF [C1206C333K1RACT U]	33 nF [C1210C333K1RACT U]	33 nF [C1812C333K2RACT U]	33 nF [GMC5.7332K250J3 1TR12]
33 nF [C1206C333K2RACT U]	33 nF [C1210C333K2RACT U]	33 nF [C1812C333K5GACT U]	33 nF [GMC5.7333K50J31 TR12]
33 nF [C1206C333K3GACT U]	33 nF [C1210C333K3GACT U]	33 nF [C1812C333K5HACT U]	33 nF [GMC7.3332K250K3 1TR12]
33 nF [C1206C333K3HACT U]	33 nF [C1210C333K3HACT U]	33 nF [C1812C333K5RACT U]	33 nF [GMC7.3332K63K31 TR12]
33 nF [C1206C333K5HACT U]	33 nF [C1210C333K5GACT U]	33 nF [C1825C333K1RACT U]	33 nF [GMC7.3333K63K31 TR12]
33 nF [C1206C333K5RACT U]	33 nF [C1210C333K5HACT U]	33 nF [C1825C333K5RACT U]	33 nF [GPC7.3333K63K33 TR12]
33 nF [C1206C333KARACT U]	33 nF [C1210C333K5RACT U]	33 nF [C2220C333K1GACT U]	33 nF [MDC10333K100A5 2P3TUBE]
33 nF [C1206C333M1UAC TU]	33 nF [C1210C333KARACT U]	33 nF [C2220C333K2GACT U]	33 nF [MDC10333K250A5 2P3TUBE]

Multisim 14.1 Education Components

33 nF [MDC10333K400A5 2P3TUBE]	33 nF [MDK10333K50A52 P3TUBE]	33 nF [MMC7.3333K250K 35TR12]	33 Ohm [4116R-1- 330LF]
33 nF [MDC10333K50A52 P3TUBE]	33 nF [MDK15333K250B5 3P3TUBE]	33 nF [MMC7.3333K63K3 1TR12]	33 Ohm [4116R-2- 330]
33 nF [MDC10333K630A5 2P3TUBE]	33 nF [MDK15333K630B5 3P3TUBE]	33 nF [SPC10.2333K100A 31TR16]	33 Ohm [4116R-2- 330LF]
33 nF [MDC15333K100B5 3P3TUBE]	33 nF [MDS10333K100A5 2P3TUBE]	33 nF [SPC10.2333K250A 31TR16]	33 Ohm [4306M- 102-330]
33 nF [MDC15333K250B5 3P3TUBE]	33 nF [MDS10333K250A5 2P3TUBE]	33 nF [SPC12.7333K400B 31TR24]	33 Ohm [4306M- 102-330LF]
33 nF [MDC15333K400B5 3P3TUBE]	33 nF [MDS10333K400A5 2P3TUBE]	33 nF [SPC12.7333K630B 31TR24]	33 Ohm [4306R- 101-330]
33 nF [MDC15333K50B53 P3TUBE]	33 nF [MDS10333K50A52 P3TUBE]	33 nF [SPC7.3333K100K37 TR12]	33 Ohm [4306R- 102-330LF]
33 nF [MDC15333K630B5 3P3TUBE]	33 nF [MDS10333K630A5 2P3TUBE]	33 Ohm [4108R-1- 330]	33 Ohm [4306R- 102-330]
33 nF [MDK10333K100A5 2P3TUBE]	33 nF [MDS15333K100B5 3P3TUBE]	33 Ohm [4108R-1- 330LF]	33 Ohm [4308M- 102-330]
33 nF [MDK10333K250A5 2P3TUBE]	33 nF [MDS15333K250B5 3P3TUBE]	33 Ohm [4114R-1- 330]	33 Ohm [4308M- 102-330LF]
33 nF [MDK10333K400A5 2P3TUBE]	33 nF [MMC5.7333K50J3 1TR12]	33 Ohm [4114R-1- 330LF]	33 Ohm [4308R- 101-330]
		33 Ohm [4114R-2- 330LF]	33 Ohm [4308R- 101-330LF]
		33 Ohm [4116R-1- 330]	33 Ohm [4308R- 102-330]

Multisim 14.1 Education Components

33 Ohm [4308R-102-330LF]	33 Ohm [4416P-T02-330]	33 Ohm [4610X-102-330LF]	33 Ohm [4816P-T01-330LF]
33 Ohm [4309R-101-330]	33 Ohm [4420P-1-330]	33 Ohm [4610X-AP2-330LF]	33 Ohm [4816P-T02-330]
33 Ohm [4310H-101-330]	33 Ohm [4420P-T01-330]	33 Ohm [4612X-102-330LF]	33 Ohm [4816P-T02-330LF]
33 Ohm [4310H-101-330LF]	33 Ohm [4604X-102-330LF]	33 Ohm [4614X-102-330LF]	33 Ohm [4818P-T01-330]
33 Ohm [4310H-102-330]	33 Ohm [4605X-101-330LF]	33 Ohm [4814P-1-330]	33 Ohm [4820P-1-330]
33 Ohm [4310H-102-330LF]	33 Ohm [4606X-101-330LF]	33 Ohm [4814P-1-330LF]	33 Ohm [4820P-T01-330]
33 Ohm [4310M-102-330]	33 Ohm [4606X-102-330LF]	33 Ohm [4814P-T01-330]	33 Ohm [4820P-T01-330LF]
33 Ohm [4310R-101-330]	33 Ohm [4608H-102-330LF]	33 Ohm [4814P-T01-330LF]	33 Ohm [CAT10-330J4LF]
33 Ohm [4310R-101-330LF]	33 Ohm [4608M-102-330LF]	33 Ohm [4814P-T02-330]	33 Ohm [CAT16-330J2LF]
33 Ohm [4310R-102-330]	33 Ohm [4608X-101-330LF]	33 Ohm [4816P-1-330]	33 Ohm [CAT16-330J4GLF]
33 Ohm [4310R-102-330LF]	33 Ohm [4608X-102-330LF]	33 Ohm [4816P-1-330G]	33 Ohm [CAT16-330J4LF]
33 Ohm [4416P-1-330]	33 Ohm [4608X-AP2-330LF]	33 Ohm [4816P-1-330LF]	33 Ohm [CAT16-330J8LF]
33 Ohm [4416P-1-330LF]	33 Ohm [4609X-101-330LF]	33 Ohm [4816P-2-330]	33 Ohm [CAT16-33R0F4LF]
33 Ohm [4416P-T01-330]	33 Ohm [4610H-101-330LF]	33 Ohm [4816P-2-330LF]	33 Ohm [CAT16-33R0F8LF]
33 Ohm [4416P-T01-330LF]	33 Ohm [4610X-101-330LF]	33 Ohm [4816P-T01-330]	33 Ohm [CAT25-330JALF]

Multisim 14.1 Education Components

33 Ohm [CAY10-330J2LF]	33 Ohm [CR0805-FX-33R0GLF]	33 Ohm [CRT0805-DZ-33R0ELF]	33 Ohm [PWR221T-30-33R0J]
33 Ohm [CAY10-330J4LF]	33 Ohm [CR0805-JW-330ELF]	33 Ohm [FW10A33R0JA]	33 Ohm [PWR2615W33R0F]
33 Ohm [CAY16-330J4GLF]	33 Ohm [CR0805-JW-330GLF]	33 Ohm [FW20A33R0JA]	33 Ohm [PWR2615W33R0F E]
33 Ohm [CAY16-330J4LF]	33 Ohm [CR1206-FX-33R0ELF]	33 Ohm [FW30A33R0JA]	33 Ohm [PWR263S-20-33R0F]
33 Ohm [CAY16-330J8LF]	33 Ohm [CR1206-FX-33R0GLF]	33 Ohm [FW50A33R0JA]	33 Ohm [PWR263S-20-33R0J]
33 Ohm [CAY16-33R0F4LF]	33 Ohm [CR1206-JW-330ELF]	33 Ohm [FW70A33R0JA]	33 Ohm [PWR263S-20-33R0J]
33 Ohm [CAY17-330JALF]	33 Ohm [CR2010-FX-33R0ELF]	33 Ohm [PWR163S-25-33R0F]	33 Ohm [PWR263S-35-33R0F]
33 Ohm [CR0201-FW-33R0GLF]	33 Ohm [CR2010-JW-330ELF]	33 Ohm [PWR163S-25-33R0J]	33 Ohm [PWR263S-35-33R0J]
33 Ohm [CR0201-JW-330GLF]	33 Ohm [CR2512-JW-330ELF]	33 Ohm [PWR2010W33R0JE]	33 Ohm [PWR263S-35-33R0JE]
33 Ohm [CR0402-FX-33R0GLF]	33 Ohm [CRM1206-FX-33R0ELF]	33 Ohm [PWR220T-20-33R0F]	33 Ohm [PWR4318W33R0J]
33 Ohm [CR0402-JW-330GLF]	33 Ohm [CRM1206-JW-330ELF]	33 Ohm [PWR220T-20-33R0J]	33 Ohm [PWR4318W33R0JE]
33 Ohm [CR0603-FX-33R0ELF]	33 Ohm [CRM2512-FX-33R0ELF]	33 Ohm [PWR220T-35-33R0J]	33 Ohm [PWR4525W33R0J]
33 Ohm [CR0603-JW-330ELF]	33 Ohm [CRM2512-JW-330ELF]	33 Ohm [PWR221T-30-33R0F]	33 Ohm [PWR6327W33R0J]
33 Ohm [CR0603-JW-330GLF]	33 Ohm [CRS1206-FX-33R0ELF]		

Multisim 14.1 Education Components

33 Ohm [W1M33R0J]	33 pF [C0603C330K3GACT U]	33 pF [C1206C330KCGAC TU]	33 uF [16TQC33MYFD]
33 Ohm [WS1A33R0J]	33 pF [C0603C330K5GACT U]	33 pF [C1206C330KDGAC TU]	33 uF [16TQC33MYFS]
33 Ohm [WS1M33R0J]	33 pF [C0805C330K1GACT U]	33 pF [C1206C330KGGAC TU]	33 uF [20SVP33M]
33 Ohm [WS3M33R0J]	33 pF [C0805C330K2GACT U]	33 pF [C1210C330KBGAC TU]	33 uF [25TQC33MYF]
33 pF [C0201C330K3GACT U]	33 pF [C0805C330K5GACT U]	33 pF [C1812C330KBGAC TU]	33 uF [A700V336M006AT E018]
33 pF [C0402C330K3GACT U]	33 pF [C0805C330KBGAC TU]	33 pF [C1825C330KBGAC TU]	33 uF [A700V336M006AT E025]
33 pF [C0402C330K4GACT U]	33 pF [C0805C330KDGAC TU]	33 pF [C2220C330KBGAC TU]	33 uF [A700V336M006AT E028]
33 pF [C0402C330K5GACT U]	33 pF [C1206C330K1GACT U]	33 pF [C2225C330KBGAC TU]	33 uF [A700V336M008AT E018]
33 pF [C0402C330K8GACT U]	33 pF [C1206C330K2GACT U]	33 pF [CA064C330K5GAC TU]	33 uF [A700V336M008AT E025]
33 pF [C0603C330K1GACT U]	33 pF [C1206C330K5GACT U]	33 pF [CA064C330K8GAC TU]	33 uF [A700V336M010AT E018]
33 pF [C0603C330K2GACT U]	33 pF [C1206C330KBGAC TU]	33 uF [10TPB33M]	33 uF [A700V336M010AT E025]
		33 uF [12TPG33M]	

Multisim 14.1 Education Components

33 uF [A700V336M010AT E028]	33 uF [EEHZC1H330XP]	33 uF [T491B336M010AT]	33 uF [T491T336M004AT]
33 uF [ATPH33MAHA]	33 uF [EEHZC1J330P]	33 uF [T491B336M016AT]	33 uF [T491T336M006AT]
33 uF [EEFCS1C330R]	33 uF [T409F336M004AH 4250]	33 uF [T491C336M004AT]	33 uF [T491T336M010AT]
33 uF [EEFCT1D330R]	33 uF [T409G336M010AH 4250]	33 uF [T491C336M006AT]	33 uF [T491U336M004AT]
33 uF [EEFCX1C330R]	33 uF [T419E336M006AH 4250]	33 uF [T491C336M010AT]	33 uF [T491U336M006AT]
33 uF [EEFCX1D330R]	33 uF [T419X336M025AH 4250]	33 uF [T491C336M016AT]	33 uF [T491U336M010AT]
33 uF [EEFCX1E330R]	33 uF [T489D336M020AT E250]	33 uF [T491C336M020AT]	33 uF [T491U336M016AT]
33 uF [EEFHX1C330R]	33 uF [T491A336M003AT]	33 uF [T491D336M010AT]	33 uF [T491V336M010AT]
33 uF [EEFHX1D330R]	33 uF [T491A336M004AT]	33 uF [T491D336M016AT]	33 uF [T491V336M020AT]
33 uF [EEFHX1E330R]	33 uF [T491A336M006AT]	33 uF [T491D336M020AT]	33 uF [T491X336M025AT]
33 uF [EEHZA1E330R]	33 uF [T491A336M010AT]	33 uF [T491D336M025AT]	33 uF [T494A336M003AT]
33 uF [EEHZA1H330XP]	33 uF [T491B336M004AT]	33 uF [T491D336M035AT]	33 uF [T494A336M004AT]
33 uF [EEHZA1J330P]	33 uF [T491B336M006AT]		33 uF [T494A336M006AT]
33 uF [EEHZA1K330P]			
33 uF [EEHZC1E330R]			

Multisim 14.1 Education Components

33 uF [T494A336M010AT]	33 uF [T494D336M035AT]	33 uF [T495C336M016AT E200]	33 uF [T495V336M010AT E150]
33 uF [T494B336M004AT]	33 uF [T494T336M004AT]	33 uF [T495C336M016AT E275]	33 uF [T495X336M025AT E100]
33 uF [T494B336M006AT]	33 uF [T494T336M006AT]	33 uF [T495D336M016AT E225]	33 uF [T495X336M025AT E175]
33 uF [T494B336M010AT]	33 uF [T494T336M010AT]	33 uF [T495D336M020AT E100]	33 uF [T495X336M025AT E200]
33 uF [T494C336M004AT]	33 uF [T494U336M004AT]	33 uF [T495D336M020AT E200]	33 uF [T495X336M035AT E100]
33 uF [T494C336M006AT]	33 uF [T494U336M006AT]	33 uF [T495D336M025AT E090]	33 uF [T495X336M035AT E175]
33 uF [T494C336M010AT]	33 uF [T494U336M010AT]	33 uF [T495D336M025AT E100]	33 uF [T495X336M035AT E250]
33 uF [T494C336M016AT]	33 uF [T494U336M016AT]	33 uF [T495D336M025AT E225]	33 uF [T497H336M015AT 6110]
33 uF [T494C336M020AT]	33 uF [T494V336M010AT]	33 uF [T495D336M025AT E300]	33 uF [T498B336M006AT E1K7]
33 uF [T494C336M025AT]	33 uF [T494V336M020AT]	33 uF [T495E336M035AT E200]	33 uF [T498D336M016AT E600]
33 uF [T494D336M010AT]	33 uF [T494X336M025AT]	33 uF [T495V336M010AT E100]	33 uF [T498D336M025AT E600]
33 uF [T494D336M016AT]	33 uF [T494X336M035AT]		
33 uF [T494D336M020AT]	33 uF [T495B336M010AT E450]		
33 uF [T494D336M025AT]			

Multisim 14.1 Education Components

33 uF [T498X336M035AT E500]	33 uF [T520B336M008AT E025]	33 uF [T520T336M010AT E070]	33 uF [T525B336M006AT E080]
33 uF [T510X336M035AT E050]	33 uF [T520B336M008AT E035]	33 uF [T520T336M010AT E080]	33 uF [T525B336M010AT E080]
33 uF [T510X336M035AT E065]	33 uF [T520B336M008AT E040]	33 uF [T520U336M008AT E070]	33 uF [T525T336M008AT E080]
33 uF [T520A336M004AT E070]	33 uF [T520B336M008AT E070]	33 uF [T520U336M010AT E070]	33 uF [T525T336M010AT E080]
33 uF [T520A336M004AT E080]	33 uF [T520B336M010AT E035]	33 uF [T520V336M016AT E045]	33 uF [T528I336M010ATE 150]
33 uF [T520A336M006AT E070]	33 uF [T520B336M010AT E040]	33 uF [T520V336M016AT E060]	33 uF [T541X336M050AH 6510]
33 uF [T520A336M006AT E080]	33 uF [T520B336M010AT E070]	33 uF [T520V336M016AT E070]	33 uF [T543A336M004AT E070]
33 uF [T520B336M006AT E025]	33 uF [T520C336M006AT E100]	33 uF [T520W336M016AT E045]	33 uF [T543B336M010AT E040]
33 uF [T520B336M006AT E035]	33 uF [T520T336M006AT E070]	33 uF [T521D336M025AT E060]	33 uF [TACR336K002RTA]
33 uF [T520B336M006AT E040]	33 uF [T520T336M008AT E070]	33 uF [T521D336M035AT E065]	33 uF [TACR336K003RTA]
33 uF [T520B336M006AT E070]	33 uF [T520T336M008AT E080]	33 uF [T521V336M025AT E060]	33 uF [TACR336K004RTA]
			33 uF [TACR336K006RTA]

Multisim 14.1 Education Components

33 uF [TAJA336K004RNJ]	33 uF [TAJD336K035RNJ]	33 uF [THJC336K016RJN]	33 uF [TPSC336K010R0150]
33 uF [TAJA336K006RNJ]	33 uF [TAJE336K025RNJ]	33 uF [THJD336K020RJN]	33 uF [TPSC336K010R0375]
33 uF [TAJA336K010RNJ]	33 uF [TAJE336K035RNJ]	33 uF [THJE336K035RJN]	33 uF [TPSC336K010R0500]
33 uF [TAJB336K004RNJ]	33 uF [TAJP336K002RNJ]	33 uF [TPME336K035R0050]	33 uF [TPSC336K016R0225]
33 uF [TAJB336K006RNJ]	33 uF [TAJS336K004RNJ]	33 uF [TPME336K035R0065]	33 uF [TPSC336K016R0300]
33 uF [TAJB336K010RNJ]	33 uF [TAJT336K006RNJ]	33 uF [TPSA336K006R0600]	33 uF [TPSC336K020R0300]
33 uF [TAJB336K016RNJ]	33 uF [TAJV336K035RNJ]	33 uF [TPSB336K006R0450]	33 uF [TPSD336K016R0200]
33 uF [TAJC336K006RNJ]	33 uF [TAJW336K006RNJ]	33 uF [TPSB336K006R0600]	33 uF [TPSD336K020R0100]
33 uF [TAJC336K010RNJ]	33 uF [TAJW336K010RNJ]	33 uF [TPSB336K010R0250]	33 uF [TPSD336K020R0200]
33 uF [TAJC336K016RNJ]	33 uF [TAJW336K016RNJ]	33 uF [TPSB336K010R0425]	33 uF [TPSD336K025R0100]
33 uF [TAJD336K010RNJ]	33 uF [TAJY336K020RNJ]	33 uF [TPSB336K010R0500]	33 uF [TPSD336K025R0200]
33 uF [TAJD336K016RNJ]	33 uF [TAJY336K025RNJ]	33 uF [THJB336K006RJN]	
33 uF [TAJD336K020RNJ]	33 uF [THJB336K006RJN]	33 uF [THJC336K010RJN]	
33 uF [TAJD336K025RNJ]			

Multisim 14.1 Education Components

33 uF [TPSD336K025R030 0]	33 uF [TPSW336K010R03 50]	33 uF [TRMD336K025R00 65]	33 uH [SDR1006- 330KL]
33 uF [TPSD336K035R020 0]	33 uF [TPSW336K016R01 75]	33 uF [TRME336K035R00 65]	33 uH [SDR1030- 330M]
33 uF [TPSD336K035R030 0]	33 uF [TPSW336K016R02 50]	33 uH [SDE0403A- 330K]	33 uH [SDR1105- 330KL]
33 uF [TPSE336K025R010 0]	33 uF [TPSW336K016R04 00]	33 uH [SDE0604A- 330M]	33 uH [SDR1305- 330M]
33 uF [TPSE336K025R017 5]	33 uF [TPSW336K016R05 00]	33 uH [SDE0805A- 330M]	33 uH [SDR1307- 330KL]
33 uF [TPSE336K025R020 0]	33 uF [TPSY336K016R030 0]	33 uH [SDE1006A- 330M]	33 uH [SDR1307A- 330K]
33 uF [TPSE336K025R030 0]	33 uF [TPSY336K016R040 0]	33 uH [SDR0302- 330KL]	33 uH [SDR1806- 330ML]
33 uF [TPSE336K035R010 0]	33 uF [TRJB336K006RRJ]	33 uH [SDR0403- 330KL]	33 uH [SDR6603- 330M]
33 uF [TPSE336K035R025 0]	33 uF [TRJB336K010RRJ]	33 uH [SDR0503- 330KL]	33 uH [SDR7030- 330M]
33 uF [TPSE336K035R030 0]	33 uF [TRJC336K010RRJ]	33 uH [SDR0603- 330KL]	33 uH [SDR7045- 330M]
33 uF [TPST336K006R080 0]	33 uF [TRJE336K035RRJ]	33 uH [SDR0604- 330KL]	33 uH [SRN1060- 330M]
		33 uH [SDR0703- 330KL]	33 uH [SRN3010- 330M]
		33 uH [SDR0805- 330KL]	33 uH [SRN3015- 330M]
		33 uH [SDR0906- 330KL]	33 uH [SRN4018- 330M]
		33 uH [SDR1005- 330KL]	

Multisim 14.1 Education Components

33 uH [SRN4026-330M]	33 uH [SRR0905-330Y]	33 uH [SRR3011-330YL]	33 uH [SRU1038A-330Y]
33 uH [SRN5020-330M]	33 uH [SRR0906-330ML]	33 uH [SRR4011-330YL]	33 uH [SRU1048-330Y]
33 uH [SRN5040-330M]	33 uH [SRR0908-330ML]	33 uH [SRR4018-330Y]	33 uH [SRU1048A-330Y]
33 uH [SRN6028-330M]	33 uH [SRR1003-330M]	33 uH [SRR4028-330Y]	33 uH [SRU1063-330Y]
33 uH [SRN6045-330M]	33 uH [SRR1005-330Y]	33 uH [SRR5018-330Y]	33 uH [SRU2011-330Y]
33 uH [SRN8040-330M]	33 uH [SRR1205-330ML]	33 uH [SRR5028-330Y]	33 uH [SRU2013-330Y]
33 uH [SRP1038A-330M]	33 uH [SRR1206-330YL]	33 uH [SRR6028-330Y]	33 uH [SRU2016-330Y]
33 uH [SRP1770TA-330M]	33 uH [SRR1208-330YL]	33 uH [SRR6038-330Y]	33 uH [SRU3017-330Y]
33 uH [SRR0603-330KL]	33 uH [SRR1210-330M]	33 uH [SRR6040A-330M]	33 uH [SRU3028-330Y]
33 uH [SRR0604-330KL]	33 uH [SRR1210A-330M]	33 uH [SRR6603-330ML]	33 uH [SRU3028A-330Y]
33 uH [SRR0618-330ML]	33 uH [SRR1240-330M]	33 uH [SRR7032-330M]	33 uH [SRU5011-330Y]
33 uH [SRR0735A-330M]	33 uH [SRR1260-330M]	33 uH [SRR7045-330M]	33 uH [SRU5016-330Y]
33 uH [SRR0745A-330M]	33 uH [SRR1260A-330M]	33 uH [SRU1028-330Y]	33 uH [SRU5018-330Y]
33 uH [SRR0804-330Y]	33 uH [SRR1280-330M]	33 uH [SRU1028A-330Y]	33 uH [SRU5028-330Y]
33 uH [SRR0805-330Y]	33 uH [SRR1806-330M]	33 uH [SRU1038-330Y]	33 uH [SRU5028A-330Y]

Multisim 14.1 Education Components

33 uH [SRU6011-330Y]	33.2 kOhm [CRM2512-FX-3322ELF]	33.2 Ohm [CRM1206-FX-33R2ELF]	330 kOhm [4308R-102-334]
33 uH [SRU6018-330Y]	33.2 kOhm [CRT0402-FZ-3322GLF]	33.2 Ohm [CRT0402-FZ-33R2GLF]	330 kOhm [4308R-102-334LF]
33 uH [SRU6025-330Y]	33.2 kOhm [CRT0603-BX-3322ELF]	330 kOhm [4114R-1-334]	330 kOhm [4309R-101-334]
33 uH [SRU6025A-330Y]	33.2 kOhm [CRT0805-BY-3322ELF]	330 kOhm [4114R-1-334LF]	330 kOhm [4310R-101-334]
33 uH [SRU8028-330Y]	33.2 kOhm [CRT0805-DZ-3322ELF]	330 kOhm [4116R-1-334]	330 kOhm [4310R-101-334LF]
33 uH [SRU8028A-330Y]	33.2 kOhm [CRT0805-DZ-3322ELF]	330 kOhm [4116R-1-334LF]	330 kOhm [4310R-102-334]
33 uH [SRU8043-330Y]	33.2 kOhm [CRT1206-FZ-3322ELF]	330 kOhm [4116R-2-334]	330 kOhm [4310R-102-334LF]
33.2 kOhm [CAY16-3322F4LF]	33.2 Ohm [CAT16-33R2F4LF]	330 kOhm [4116R-2-334LF]	330 kOhm [4420P-2-334]
33.2 kOhm [CR0402-FX-3322GLF]	33.2 Ohm [CAY16-33R2F4LF]	330 kOhm [4306M-102-334]	330 kOhm [4420P-T02-334]
33.2 kOhm [CR0603-FX-3322ELF]	33.2 Ohm [CR0402-FX-33R2GLF]	330 kOhm [4306R-101-334]	330 kOhm [4604X-102-334LF]
33.2 kOhm [CR0805-FX-3322ELF]	33.2 Ohm [CR0603-FX-33R2ELF]	330 kOhm [4306R-101-334LF]	330 kOhm [4605X-101-334LF]
33.2 kOhm [CR1206-FX-3322ELF]	33.2 Ohm [CR0805-FX-33R2ELF]	330 kOhm [4306R-102-334]	330 kOhm [4606M-101-334LF]
33.2 kOhm [CR2512-FX-3322ELF]	33.2 Ohm [CR1206-FX-33R2ELF]	330 kOhm [4306R-102-334LF]	330 kOhm [4606X-101-334LF]
	33.2 Ohm [CR2512-FX-33R2ELF]	330 kOhm [4308R-101-334]	330 kOhm [4608X-101-334LF]
		330 kOhm [4308R-101-334LF]	

Multisim 14.1 Education Components

330 kOhm [4608X-102-334LF]	330 kOhm [CAT16-3303F4LF]	330 kOhm [CR0805-JW-334ELF]	330 mOhm [CRL1206-FW-R330ELF]
330 kOhm [4609X-101-334LF]	330 kOhm [CAT16-334J4LF]	330 kOhm [CR0805-JW-334GLF]	330 mOhm [CRL1206-JW-R330ELF]
330 kOhm [4610X-101-334LF]	330 kOhm [CAT25-334JALF]	330 kOhm [CR1206-FX-3303ELF]	330 mOhm [CRL2010-FW-R330ELF]
330 kOhm [4610X-102-334LF]	330 kOhm [CAY10-334J4LF]	330 kOhm [CR1206-JW-334ELF]	330 mOhm [CRL2010-JW-R330ELF]
330 kOhm [4612X-101-334LF]	330 kOhm [CAY16-3303F4LF]	330 kOhm [CR1206-JW-334GLF]	330 mOhm [CRL2512-FW-R330ELF]
330 kOhm [4816P-1-334]	330 kOhm [CAY16-334J4LF]	330 kOhm [CRT0805-BY-3303ELF]	330 mOhm [CRL2512-JW-R330ELF]
330 kOhm [4816P-1-334LF]	330 kOhm [CAY16-334J8LF]	330 kOhm [CRT1206-BY-3303ELF]	330 mOhm [CRM1206-FX-R330ELF]
330 kOhm [4816P-2-334]	330 kOhm [CHV0603-JW-334ELF]	330 mOhm [CRL0603-FW-R330ELF]	330 mOhm [CRM2512-FX-R330ELF]
330 kOhm [4816P-2-334LF]	330 kOhm [CHV0805-JW-334ELF]	330 mOhm [CRL0603-JW-R330ELF]	330 mOhm [PWR163S-25-R330FE]
330 kOhm [4816P-T01-334]	330 kOhm [CR0402-FX-3303GLF]	330 mOhm [CRL0805-FW-R330ELF]	330 mOhm [PWR221T-30-R330F]
330 kOhm [4816P-T01-334LF]	330 kOhm [CR0603-FX-3303ELF]	330 mOhm [CRL0805-JW-R330ELF]	
330 kOhm [4816P-T02-334]	330 kOhm [CR0603-JW-334ELF]		
330 kOhm [4816P-T02-334LF]	330 kOhm [CR0805-FX-3303ELF]		
330 kOhm [CAT10-334J4LF]			

Multisim 14.1 Education Components

330 mOhm [PWR263S-35- R330F]	330 nF [C0805C334M4VAC TU]	330 nF [C1210C334K5RACT U]	330 nF [C1812F334K1RACT U]
330 nF [C0603C334K4PACT U]	330 nF [C0805C334M8VAC TU]	330 nF [C1210C334M5UAC TU]	330 nF [C1812F334K2RACT U]
330 nF [C0603C334K4RACT U]	330 nF [C1206C334K1RACT U]	330 nF [C1210C334M5VAC TU]	330 nF [C1812F334K3RACT U]
330 nF [C0603C334K8PACT U]	330 nF [C1206C334K3RACT U]	330 nF [C1210F334K1RACT U]	330 nF [C1812F334K5RACT U]
330 nF [C0603C334K8RACT U]	330 nF [C1206C334K4RACT U]	330 nF [C1210F334K3RACT U]	330 nF [C1825C334K1RACT U]
330 nF [C0603C334K9RACT U]	330 nF [C1206C334K5RACT U]	330 nF [C1210F334K4RACT U]	330 nF [C1825C334K2RACT U]
330 nF [C0805C334K3NAC TU]	330 nF [C1206C334M3VAC TU]	330 nF [C1210F334K5RACT U]	330 nF [C1825C334K5RACT U]
330 nF [C0805C334K3RACT U]	330 nF [C1206F334K3RACT U]	330 nF [C1812C334K1RACT U]	330 nF [C1825C334M5UAC TU]
330 nF [C0805C334K4RACT U]	330 nF [C1206F334K4RACT U]	330 nF [C1812C334K5RACT U]	330 nF [C2220C334K1GACT U]
330 nF [C0805C334K8RACT U]	330 nF [C1210C334K1RACT U]	330 nF [C1812C334KARACT U]	330 nF [C2220C334K1RACT U]
330 nF [C0805C334M3VAC TU]	330 nF [C1210C334K3RACT U]	330 nF [C1812C334M5UAC TU]	330 nF [C2220C334K2RACT U]

Multisim 14.1 Education Components

330 nF [C2220C334K5GACT U]	330 nF [MDC10334K400A5 7P8TUBE]	330 nF [MDS10334K250A5 2P3TUBE]	330 nF [T491B334M050AT]
330 nF [C2220C334K5RACT U]	330 nF [MDC10334K50A52 P3TUBE]	330 nF [MDS10334K50A52 P3TUBE]	330 nF [T494A334M025AT]
330 nF [C2225C334K1RACT U]	330 nF [MDC15334K100B5 3P3TUBE]	330 nF [MDS15334K100B5 3P3TUBE]	330 nF [T494A334M035AT]
330 nF [C2225C334K2RACT U]	330 nF [MDC15334K250B5 3P3TUBE]	330 nF [MDS15334K250B5 3P3TUBE]	330 nF [T496B334M050AT 6110]
330 nF [C2225C334K5RACT U]	330 nF [MDC15334K400B5 5P3TUBE]	330 nF [PG224D334MAB2S 1]	330 nF [TAJA334K035RNJ]
330 nF [C2225C334M5UAC TU]	330 nF [MDC15334K400B5 5P4TUBE]	330 nF [PG224W334MAB2 S1]	330 nF [TAJB334K050RNJ]
330 nF [GMC7.3334K63K35 TR12]	330 nF [MDC15334K50B53 P3TUBE]	330 nF [PG224Z334MAB2S 1]	330 nF [TAJR334K025RNJ]
330 nF [LG224Z334MAT2S 1]	330 nF [MDK10334K100A5 2P3TUBE]	330 nF [SPC16.5334K100C 31TR24]	330 nF [TAJR334K035RNJ]
330 nF [MDC10334K100A5 2P3TUBE]	330 nF [MDK10334K250A5 2P3TUBE]	330 nF [SPC16.5334K250C 31TR24]	330 nF [TAJS334K020RNJ]
330 nF [MDC10334K250A5 2P3TUBE]	330 nF [MDK10334K50A52 P3TUBE]	330 nF [T409A334M025AH 4250]	330 nF [THJA334K035RJN]
330 nF [MDC10334K400A5 7P7TUBE]	330 nF [MDS10334K100A5 2P3TUBE]	330 nF [T491A334M025AT]	330 nF [TPSA334K035R600 0]
		330 nF [T491A334M035AT]	

Multisim 14.1 Education Components

330 nF [W2L1ZC334MAT1A]	330 Ohm [4114R-2- 331]	330 Ohm [4306R- 102-331LF]	330 Ohm [4310H- 101-331LF]
330 nF [W3L1YC334MAT1A]	330 Ohm [4114R-2- 331LF]	330 Ohm [4308H- 101-331]	330 Ohm [4310M- 101-331]
330 nH [SRN2512- R33M]	330 Ohm [4116R-1- 331]	330 Ohm [4308H- 102-331]	330 Ohm [4310M- 101-331LF]
330 nH [SRP1235- R33M]	330 Ohm [4116R-2- 331]	330 Ohm [4308M- 101-331]	330 Ohm [4310M- 102-331LF]
330 nH [SRP1245A- R33M]	330 Ohm [4116R-2- 331LF]	330 Ohm [4308M- 101-331LF]	330 Ohm [4310R- 101-331]
330 nH [SRP1265A- R33M]	330 Ohm [4306H- 101-331]	330 Ohm [4308M- 102-331]	330 Ohm [4310R- 101-331LF]
330 nH [SRP4020TA-R33M]	330 Ohm [4306H- 101-331LF]	330 Ohm [4308M- 102-331LF]	330 Ohm [4310R- 102-331]
330 nH [SRP5015TA-R33M]	330 Ohm [4306H- 102-331]	330 Ohm [4308R- 101-331]	330 Ohm [4310R- 102-331LF]
330 nH [SRP5030TA-R33M]	330 Ohm [4306H- 102-331LF]	330 Ohm [4308R- 101-331LF]	330 Ohm [4311R- 101-331]
330 nH [SRP5030T- R33M]	330 Ohm [4306M- 101-331]	330 Ohm [4308R- 102-331]	330 Ohm [4416P-1- 331]
330 nH [SRP7028A- R33M]	330 Ohm [4306M- 102-331]	330 Ohm [4308R- 102-331LF]	330 Ohm [4416P-1- 331LF]
330 nH [SRP7030- R33FM]	330 Ohm [4306R- 101-331]	330 Ohm [4309R- 101-331]	330 Ohm [4416P-2- 331]
330 nH [SRP7050TA-R33M]	330 Ohm [4306R- 101-331LF]	330 Ohm [4309R- 101-331LF]	330 Ohm [4416P- T01-331]
330 Ohm [4114R-1- 331]	330 Ohm [4306R- 102-331]	330 Ohm [4310H- 101-331]	330 Ohm [4416P- T01-331LF]
330 Ohm [4114R-1- 331LF]			

Multisim 14.1 Education Components

330 Ohm [4416P-T02-331]	330 Ohm [4607X-101-331LF]	330 Ohm [4614X-102-331LF]	330 Ohm [4816P-T01-331LF]
330 Ohm [4420P-1-331]	330 Ohm [4608H-102-331LF]	330 Ohm [4814P-1-331]	330 Ohm [4816P-T02-331]
330 Ohm [4420P-2-331]	330 Ohm [4608M-102-331LF]	330 Ohm [4814P-1-331LF]	330 Ohm [4816P-T02-331LF]
330 Ohm [4420P-2-331LF]	330 Ohm [4608X-101-331LF]	330 Ohm [4814P-2-331]	330 Ohm [4820P-1-331]
330 Ohm [4420P-T01-331]	330 Ohm [4608X-102-331LF]	330 Ohm [4814P-2-331LF]	330 Ohm [4820P-1-331LF]
330 Ohm [4420P-T02-331]	330 Ohm [4608X-AP2-331LF]	330 Ohm [4814P-T01-331]	330 Ohm [4820P-2-331]
330 Ohm [4604X-101-331LF]	330 Ohm [4609X-101-331LF]	330 Ohm [4814P-T01-331LF]	330 Ohm [4820P-T01-331]
330 Ohm [4604X-102-331LF]	330 Ohm [4609X-AP1-331LF]	330 Ohm [4814P-T02-331]	330 Ohm [4820P-T01-331LF]
330 Ohm [4605X-101-331LF]	330 Ohm [4610H-101-331LF]	330 Ohm [4814P-T02-331LF]	330 Ohm [4820P-T02-331]
330 Ohm [4605X-AP1-331LF]	330 Ohm [4610H-102-331LF]	330 Ohm [4816P-1-331]	330 Ohm [4820P-T02-331LF]
330 Ohm [4606H-101-331LF]	330 Ohm [4610M-101-331LF]	330 Ohm [4816P-1-331LF]	330 Ohm [CAT10-331J4LF]
330 Ohm [4606M-101-331LF]	330 Ohm [4610X-101-331LF]	330 Ohm [4816P-2-331]	330 Ohm [CAT16-3300F4LF]
330 Ohm [4606X-101-331LF]	330 Ohm [4610X-102-331LF]	330 Ohm [4816P-2-331F]	330 Ohm [CAT16-3300F8LF]
330 Ohm [4606X-102-331LF]	330 Ohm [4611X-101-331LF]	330 Ohm [4816P-2-331LF]	330 Ohm [CAT16-331J2LF]
330 Ohm [4606X-AP1-331LF]	330 Ohm [4612X-102-331LF]	330 Ohm [4816P-T01-331]	330 Ohm [CAT16-331J4GLF]

Multisim 14.1 Education Components

330 Ohm [CAT16-331J4LF]	330 Ohm [CR0805-FX-3300ELF]	330 Ohm [PWR220T-20-3300F]	330 pF [C0402C331K1HACTU]
330 Ohm [CAT16-331J8LF]	330 Ohm [CR0805-FX-3300GLF]	330 Ohm [PWR220T-20-3300J]	330 pF [C0402C331K3HACTU]
330 Ohm [CAT25-331JALF]	330 Ohm [CR0805-JW-331ELF]	330 Ohm [PWR220T-35-3300J]	330 pF [C0402C331K3RACTU]
330 Ohm [CAY10-331J4LF]	330 Ohm [CR0805-JW-331GLF]	330 Ohm [PWR263S-20-3300F]	330 pF [C0402C331K4GACTU]
330 Ohm [CAY16-331J4LF]	330 Ohm [CR1206-JW-331ELF]	330 Ohm [PWR263S-20-3300J]	330 pF [C0402C331K4RACTU]
330 Ohm [CAY16-331J8LF]	330 Ohm [CR1206-JW-331GLF]	330 Ohm [PWR263S-20-3300JE]	330 pF [C0402C331K5GACTU]
330 Ohm [CAY17-331JALF]	330 Ohm [CR2512-FX-3300ELF]	330 Ohm [PWR263S-35-3300F]	330 pF [C0402C331K5HACTU]
330 Ohm [CR0201-JW-331GLF]	330 Ohm [CR2512-JW-331ELF]	330 Ohm [PWR263S-35-3300J]	330 pF [C0402C331K5RACTU]
330 Ohm [CR0402-FX-3300GLF]	330 Ohm [CRM2512-FX-3300ELF]	330 Ohm [PWR263S-35-3300JE]	330 pF [C0603C331K1RACTU]
330 Ohm [CR0402-JW-331GLF]	330 Ohm [CRT0603-BY-3300ELF]	330 Ohm [PWR5322W3300FE]	330 pF [C0603C331K2RACTU]
330 Ohm [CR0603-FX-3300ELF]	330 Ohm [CRT0603-FY-3300ELF]	330 Ohm [PWR6327W3300J]	
330 Ohm [CR0603-FX-3300GLF]	330 Ohm [PWR163S-25-3300FE]	330 Ohm [PWR6327W330RJ]	

Multisim 14.1 Education Components

330 pF [C0603C331K3GACT U]	330 pF [C0805C331K3RACT U]	330 pF [C1210C331K5GACT U]	330 uF [2R5SVPE330MY]
330 pF [C0603C331K3RACT U]	330 pF [C0805C331K4RACT U]	330 pF [C1210C331KBGAC TU]	330 uF [2R5TPE330M]
330 pF [C0603C331K4RACT U]	330 pF [C0805C331K5GACT U]	330 pF [C1812C331KBGAC TU]	330 uF [2R5TPE330M9]
330 pF [C0603C331K5GACT U]	330 pF [C0805C331K5RACT U]	330 pF [C1825C331KBGAC TU]	330 uF [2R5TPE330MAZB]
330 pF [C0603C331K5RACT U]	330 pF [C0805C331K8RACT U]	330 pF [C2220C331KBGAC TU]	330 uF [2R5TPE330MC]
330 pF [C0603C331K8RACT U]	330 pF [C1206C331K1GACT U]	330 pF [C2225C331KBGAC TU]	330 uF [2R5TPE330MI]
330 pF [C0805C331K1GACT U]	330 pF [C1206C331K2GACT U]	330 pF [CA064C331K5GAC TU]	330 uF [2R5TPF330M7L]
330 pF [C0805C331K1RACT U]	330 pF [C1206C331K5GACT U]	330 pF [CA064C331K5RACT U]	330 uF [2SEPC330MW]
330 pF [C0805C331K2GACT U]	330 pF [C1206C331KBGAC TU]	330 uF [10TPB330M]	330 uF [2TPE330MAFB]
330 pF [C0805C331K2RACT U]	330 pF [C1206C331KCGAC TU]	330 uF [10TPE330M]	330 uF [2TPE330MFB]
330 pF [C0805C331K3GACT U]	330 pF [C1210C331K1GACT U]	330 uF [16SVP330M]	330 uF [2TPF330M6]
		330 uF [2R5SVPE330M]	330 uF [4SVPC330M]

Multisim 14.1 Education Components

330 uF [4SVPC330MV]	330 uF [6TPE330ML]	330 uF [EEFGX0D331R]	330 uF [EEFSX0E331ER]
330 uF [4SVPC330MY]	330 uF [6TPF330M9L]	330 uF [EEFHX0E331R]	330 uF [EEFSX0E331XE]
330 uF [4TPB330ML]	330 uF [A700D337M002AT E007]	330 uF [EEFHX0E331R4]	330 uF [EEHZA1E331P]
330 uF [4TPE330M]	330 uF [A700X337M002AT E010]	330 uF [EEFHX0E331R6]	330 uF [EEHZC1E331P]
330 uF [4TPE330MI]	330 uF [A700X337M002AT E015]	330 uF [EEFHX0E331R9]	330 uF [T489X337M010AT E100]
330 uF [4TPF330ML]	330 uF [A700X337M002AT E015]	330 uF [EEFLT0D331R]	330 uF [T491C337M004AT]
330 uF [6SVPC330M]	330 uF [A700X337M004AT E010]	330 uF [EEFLX0D331R]	330 uF [T491D337M004AT]
330 uF [6TPB330M]	330 uF [A700X337M004AT E015]	330 uF [EEFLX0D331R4]	330 uF [T491D337M006AT]
330 uF [6TPB330MAL]	330 uF [A700X337M2R5AT E010]	330 uF [EEFLX0E331R4]	330 uF [T491D337M010AT]
330 uF [6TPB330ML]	330 uF [A700X337M2R5AT E015]	330 uF [EEFST0D331R]	330 uF [T491E337M006AT]
330 uF [6TPC330MA]	330 uF [EEFCX0D331R]	330 uF [EEFSX0D331E4]	330 uF [T491E337M010AT]
330 uF [6TPE330MAA]	330 uF [EEFCX0D331XR]	330 uF [EEFSX0D331ER]	330 uF [T491V337M004AT]
330 uF [6TPE330MAL]	330 uF [EEFCX0E331R]	330 uF [EEFSX0D331XE]	330 uF [T491X337M006AT]
330 uF [6TPE330MAP]	330 uF [EEFCX0G331R]	330 uF [EEFSX0E331E4]	330 uF [T491X337M010AT]
330 uF [6TPE330MFL]			
330 uF [6TPE330MIL]			

Multisim 14.1 Education Components

330 uF [T494C337M004AT]	330 uF [T495D337M006AT E100]	330 uF [T495X337M010AT E100]	330 uF [T520D337M004AT E009]
330 uF [T494D337M004AT]	330 uF [T495D337M010AT E100]	330 uF [T510X337M010AT E035]	330 uF [T520D337M004AT E012]
330 uF [T494D337M006AT]	330 uF [T495D337M010AT E125]	330 uF [T513X337M010AH 6110]	330 uF [T520D337M004AT E015]
330 uF [T494D337M010AT]	330 uF [T495D337M010AT E150]	330 uF [T520B337M2R5AT E045]	330 uF [T520D337M004AT E040]
330 uF [T494E337M006AT]	330 uF [T495E337M010AT E060]	330 uF [T520B337M2R5AT E070]	330 uF [T520D337M004AT E045]
330 uF [T494V337M004AT]	330 uF [T495X337M006AT E045]	330 uF [T520C337M004AT E025]	330 uF [T520D337M006AT E009]
330 uF [T494X337M006AT]	330 uF [T495X337M006AT E065]	330 uF [T520C337M2R5AT E015]	330 uF [T520D337M006AT E010]
330 uF [T494X337M010AT]	330 uF [T495X337M006AT E100]	330 uF [T520C337M2R5AT E025]	330 uF [T520D337M006AT E015]
330 uF [T495D337M004AT E030]	330 uF [T495X337M010AT E035]	330 uF [T520C337M2R5AT E045]	330 uF [T520D337M006AT E025]
330 uF [T495D337M006AT E050]	330 uF [T495X337M010AT E050]	330 uF [T520D337M004AT E006]	330 uF [T520D337M006AT E040]
330 uF [T495D337M006AT E070]	330 uF [T495X337M010AT E060]	330 uF [T520D337M004AT E007]	330 uF [T520D337M006AT E045]

Multisim 14.1 Education Components

330 uF [T520D337M2R5AT E006]	330 uF [T520V337M004AT E012]	330 uF [T520V337M2R5AT E015]	330 uF [T520Y337M006AT E040]
330 uF [T520D337M2R5AT E007]	330 uF [T520V337M004AT E018]	330 uF [T520V337M2R5AT E018]	330 uF [T520Y337M010AT E015]
330 uF [T520L337M2R5AT E009]	330 uF [T520V337M004AT E025]	330 uF [T520V337M2R5AT E025]	330 uF [T520Y337M010AT E035]
330 uF [T520L337M2R5AT E012]	330 uF [T520V337M004AT E040]	330 uF [T520V337M2R5AT E040]	330 uF [T522V337M006AT E040]
330 uF [T520L337M2R5AT E025]	330 uF [T520V337M006AT E015]	330 uF [T520W337M2R5A TE025]	330 uF [T525D337M003AT E025]
330 uF [T520V337M003AT E009]	330 uF [T520V337M006AT E025]	330 uF [T520W337M2R5A TE040]	330 uF [T525D337M004AT E025]
330 uF [T520V337M003AT E012]	330 uF [T520V337M006AT E040]	330 uF [T520X337M010AT E010]	330 uF [T525D337M006AT E025]
330 uF [T520V337M003AT E015]	330 uF [T520V337M2R5AT E006]	330 uF [T520X337M010AT E025]	330 uF [T525D337M006AT E040]
330 uF [T520V337M003AT E025]	330 uF [T520V337M2R5AT E007]	330 uF [T520X337M010AT E040]	330 uF [T525D337M2R5AT E025]
330 uF [T520V337M004AT E007]	330 uF [T520V337M2R5AT E009]	330 uF [T520Y337M006AT E015]	330 uF [T528Z337M004AT E009]
330 uF [T520V337M004AT E009]	330 uF [T520V337M2R5AT E012]	330 uF [T520Y337M006AT E025]	330 uF [T528Z337M004AT E012]

Multisim 14.1 Education Components

330 uF [T528Z337M2R5AT E005]	330 uF [T530X337M010AT E010]	330 uF [TAJE337K010RNJ]	330 uF [TPSD337K006R007 0]
330 uF [T528Z337M2R5AT E007]	330 uF [T530Y337M006AT E006]	330 uF [TAJV337K010RNJ]	330 uF [TPSD337K006R010 0]
330 uF [T528Z337M2R5AT E008]	330 uF [T541X337M010AH 6520]	330 uF [TPME337K010R00 23]	330 uF [TPSD337K010R010 0]
330 uF [T528Z337M2R5AT E009]	330 uF [T541Y337M006AH 6510]	330 uF [TPME337K010R00 35]	330 uF [TPSD337K010R015 0]
330 uF [T528Z337M2R5AT E012]	330 uF [T543C337M2R5AT E045]	330 uF [TPSC337K006R008 0]	330 uF [TPSE337K006R005 0]
330 uF [T530D337M004AT E006]	330 uF [T543L337M2R5AT E025]	330 uF [TPSC337K006R010 0]	330 uF [TPSE337K006R010 0]
330 uF [T530D337M006AT E006]	330 uF [T543Y337M006AT E015]	330 uF [TPSD337K004R003 5]	330 uF [TPSE337K006R012 5]
330 uF [T530D337M006AT E010]	330 uF [TAJC337K004RNJ]	330 uF [TPSD337K004R004 5]	330 uF [TPSE337K006R015 0]
330 uF [T530X337M010AT E004]	330 uF [TAJC337K006RNJ]	330 uF [TPSD337K004R010 0]	330 uF [TPSE337K010R004 0]
330 uF [T530X337M010AT E005]	330 uF [TAJD337K006RNJ]	330 uF [TPSD337K006R004 5]	330 uF [TPSE337K010R005 0]
330 uF [T530X337M010AT E006]	330 uF [TAJD337K010RNJ]	330 uF [TPSD337K006R005 0]	330 uF [TPSE337K010R006 0]
	330 uF [TAJE337K006RNJ]		

Multisim 14.1 Education Components

330 uF [TPSE337K010R010 0]	330 uH [SDR0403- 331KL]	330 uH [SDR6603- 331M]	330 uH [SRR1205- 331KL]
330 uF [TPSV337K010R004 0]	330 uH [SDR0503- 331KL]	330 uH [SDR7030- 331K]	330 uH [SRR1206- 331KL]
330 uF [TPSV337K010R006 0]	330 uH [SDR0603- 331KL]	330 uH [SDR7045- 331K]	330 uH [SRR1208- 331KL]
330 uF [TPSV337K010R006 0]	330 uH [SDR0604- 331KL]	330 uH [SRN1060- 331M]	330 uH [SRR1210- 331M]
330 uF [TPSV337K010R010 0]	330 uH [SDR0703- 331KL]	330 uH [SRR0603- 331KL]	330 uH [SRR1210A- 331M]
330 uF [TPSV337K010R010 0]	330 uH [SDR0805- 331KL]	330 uH [SRR0604- 331KL]	330 uH [SRR1240- 331K]
330 uF [TPSY337K006R015 0]	330 uH [SDR0906- 331KL]	330 uH [SRR0735A- 331M]	330 uH [SRR1260- 331K]
330 uF [TRJD337K006RRJ]	330 uH [SDR1005- 331KL]	330 uH [SRR0745A- 331M]	330 uH [SRR1260A- 331K]
330 uF [TRJE337K006RRJ]	330 uH [SDR1006- 331KL]	330 uH [SRR0804- 331K]	330 uH [SRR1280- 331K]
330 uF [TRJE337K010RRJ]	330 uH [SDR1030- 331K]	330 uH [SRR0805- 331K]	330 uH [SRR1806- 331M]
330 uF [TRMD337K004R00 35]	330 uH [SDR1045- 331K]	330 uH [SRR0905- 331K]	330 uH [SRR4028- 331Y]
330 uF [TRME337K010R00 35]	330 uH [SDR1305- 331K]	330 uH [SRR0906- 331YL]	330 uH [SRR5028- 331Y]
330 uH [SDE0805A- 331K]	330 uH [SDR1307- 331KL]	330 uH [SRR0908- 331YL]	330 uH [SRR6028- 331Y]
330 uH [SDE1006A- 331K]	330 uH [SDR1307A-331K]	330 uH [SRR1003- 331Y]	330 uH [SRR6603- 331ML]
330 uH [SDR0302- 331KL]	330 uH [SDR1806- 331KL]	330 uH [SRR1005- 331K]	330 uH [SRR7032- 331M]

Multisim 14.1 Education Components

330 uH [SRR7045-331M]	332 Ohm [CAY16-3320F4LF]	34 kOhm [CR1206-FX-3402ELF]	34.8 Ohm [CR0603-FX-34R8ELF]
330 uH [SRU1038-331Y]	332 Ohm [CR0402-FX-3320GLF]	34 mOhm [CRA2512-JZ-R034ELF]	34.8 Ohm [CR0805-FX-34R8ELF]
330 uH [SRU1038A-331Y]	332 Ohm [CR0603-FX-3320ELF]	34 Ohm [CR0603-FX-34R0ELF]	34.8 Ohm [CR1206-FX-34R8ELF]
330 uH [SRU1048-331Y]	332 Ohm [CR0603-FX-3320GLF]	34 Ohm [CR0805-FX-34R0ELF]	34.8 Ohm [CRM2010-FX-34R8ELF]
330 uH [SRU1048A-331Y]	332 Ohm [CR0805-FX-3320ELF]	34 Ohm [CR1206-FX-34R0ELF]	340 kOhm [CR0402-FX-3403GLF]
332 kOhm [CAY16-3323F4LF]	332 Ohm [CR1206-FX-3320ELF]	34.8 kOhm [CAT16-3482F4LF]	340 kOhm [CR0603-FX-3403ELF]
332 kOhm [CR0402-FX-3323GLF]	332 Ohm [CRM2512-FX-3320ELF]	34.8 kOhm [CR0402-FX-3482GLF]	340 kOhm [CR0805-FX-3403ELF]
332 kOhm [CR0603-FX-3323ELF]	332 Ohm [CRT0402-FZ-3320GLF]	34.8 kOhm [CR0603-FX-3482ELF]	340 kOhm [CR1206-FX-3403ELF]
332 kOhm [CR0805-FX-3323ELF]	332 Ohm [CRT1206-FZ-3320ELF]	34.8 kOhm [CR0805-FX-3482ELF]	340 kOhm [CRT0603-BY-3403ELF]
332 kOhm [CR1206-FX-3323ELF]	34 kOhm [4816P-1-343]	34.8 kOhm [CR1206-FX-3482ELF]	340 kOhm [CRT1206-BY-3403ELF]
332 kOhm [CRT0603-BY-3323ELF]	34 kOhm [4816P-1-343LF]	34.8 kOhm [CRM2512-FX-3482ELF]	340 Ohm [CR0603-FX-3400ELF]
332 kOhm [CRT1206-DY-3323ELF]	34 kOhm [CR0402-FX-3402GLF]	34.8 kOhm [CRT0603-BX-3482ELF]	340 Ohm [CR0805-FX-3400ELF]
332 kOhm [CRT1206-FZ-3323ELF]	34 kOhm [CR0805-FX-3402ELF]	34.8 Ohm [CR0402-FX-34R8GLF]	340 Ohm [CR1206-FX-3400ELF]

Multisim 14.1 Education Components

340 Ohm [CRM1206-FX- 3400ELF]	35.7 kOhm [CR0603-FX- 3572ELF]	357 kOhm [CR0805-FX- 3573ELF]	35SCGQ060 35SGQ060
348 kOhm [CR0402-FX- 3483GLF]	35.7 kOhm [CR0805-FX- 3572ELF]	357 kOhm [CR1206-FX- 3573ELF]	36 kOhm [4308R- 102-363LF] 36 kOhm [4310R- 101-363]
348 kOhm [CR0603-FX- 3483ELF]	35.7 kOhm [CR1206-FX- 3572ELF]	357 Ohm [CR0402- FX-3570GLF] 357 Ohm [CR0603- FX-3570ELF]	36 kOhm [4604X- 102-363LF] 36 kOhm [CAY16- 363J4LF]
348 kOhm [CR0805-FX- 3483ELF]	35.7 kOhm [CRM2512-FX- 3572ELF]	357 Ohm [CR0805- FX-3570ELF] 357 Ohm [CR0805- FX-3570GLF]	36 kOhm [CR0201- FW-3602GLF] 36 kOhm [CR0402- FX-3602GLF]
348 kOhm [CR1206-FX- 3483ELF]	35.7 Ohm [CR0402- FX-35R7GLF] 35.7 Ohm [CR0603- FX-35R7ELF]	357 Ohm [CR1206- FX-3570ELF] 357 Ohm [CR2010- FX-3570ELF]	36 kOhm [CR0603- FX-3602ELF] 36 kOhm [CR0603- JW-363ELF]
348 kOhm [CRM2512-FX- 3483ELF]	35.7 Ohm [CR0805- FX-35R7ELF] 35.7 Ohm [CR1206- FX-35R7ELF]	357 Ohm [CR2512- FX-3570ELF] 357 Ohm [CRT1206-BY- 3570ELF]	36 kOhm [CR0805- FX-3602ELF] 36 kOhm [CR0805- JW-363ELF]
348 Ohm [CR0402- FX-3480GLF]	35.7 Ohm [CR0805- FX-35R7GLF]	357 Ohm [CR2512- FX-3570ELF]	36 kOhm [CR1206- FX-3602ELF]
348 Ohm [CR0603- FX-3480ELF]	35.7 Ohm [CR1206- FX-35R7ELF]	357 Ohm [CRT1206-BY- 3570ELF]	36 kOhm [CR1206- JW-363ELF]
348 Ohm [CR0805- FX-3480ELF]	3-534206-0	35CGQ045 35CGQ100	36 kOhm [CR1206- JW-363ELF]
348 Ohm [CR1206- FX-3480ELF]	3554AM 3554BM	35CGQ150 35CLQ045	36 mF [C0805C369KBGAC TU]
35 mOhm [CRF2512-FZ- R035ELF]	3554SM 357 kOhm [CR0402-FX- 3573GLF]	35GQ100 35GQ150	36 mOhm [PWR1913WR036J]
35.7 kOhm [CR0402-FX- 3572GLF]	357 kOhm [CR0603-FX- 3573ELF]	35SCGQ030	

Multisim 14.1 Education Components

36 mOhm [PWR1913WR036JE]	36 Ohm [CAY16- 360J4LF]	36 pF [C1206C360KBGAC TU]	36.5 Ohm [CAY16- 36R5F4LF]
36 mOhm [PWR2615WR036J]	36 Ohm [CAY16- 36R0F4LF]	36 pF [C1210C360KBGAC TU]	36.5 Ohm [CR0402- FX-36R5GLF]
36 mOhm [PWR2615WR036JE]	36 Ohm [CAY17- 360JALF]	36 pF [C1812C360KBGAC TU]	36.5 Ohm [CR0603- FX-36R5ELF]
36 mOhm [PWR4525WR036J]	36 Ohm [CR0402- FX-36R0GLF]	36 pF [C1825C360KBGAC TU]	36.5 Ohm [CR0805- FX-36R5ELF]
36 mOhm [PWR4525WR036JE]	36 Ohm [CR0402- JW-360GLF]	36 pF [C1825C360KBGAC TU]	36.5 Ohm [CR1206- FX-36R5ELF]
36 mOhm [PWR6327WR036J]	36 Ohm [CR0603- FX-36R0ELF]	36 pF [C2220C360KBGAC TU]	36.5 Ohm [PWR1913W36R5F]
36 mOhm [PWR6327WR036JE]	36 Ohm [CR0603- JW-360GLF]	36 pF [C2220C360KZGACT U]	36.5 Ohm [PWR2010W36R5F E]
36 Ohm [4116R-1- 360]	36 Ohm [CR0805- FX-36R0ELF]	36 pF [C2225C360KBGAC TU]	360 kOhm [4114R- 1-364]
36 Ohm [4116R-1- 360LF]	36 Ohm [CR0805- JW-360ELF]	36.5 kOhm [CR0402-FX- 3652GLF]	360 kOhm [4114R- 1-364LF]
36 Ohm [4816P-1- 360]	36 Ohm [CR1206- FX-36R0ELF]	36.5 kOhm [CR0603-FX- 3652ELF]	360 kOhm [CAY16- 364J4LF]
36 Ohm [CAT10- 360J4LF]	36 Ohm [CR1206- JW-360ELF]	36.5 kOhm [CR0805-FX- 3652ELF]	360 kOhm [CHV0805-FX- 3603ELF]
36 Ohm [CAT16- 360J4LF]	36 Ohm [CRT0805- BW-36R0ELF]	36.5 kOhm [CR1206-FX- 3652ELF]	360 kOhm [CR0402-FX- 3603GLF]
36 Ohm [CAY10- 360J2LF]	36 Ohm [PWR6327N36R0JE]		
36 Ohm [CAY10- 360J4LF]	36 pF [C0805C360KBGAC TU]		

Multisim 14.1 Education Components

360 kOhm [CR0603-FX-3603ELF]	360 mOhm [CRL1206-JW-R360ELF]	360 mOhm [PWR6327WR360J]	360 Ohm [4816P-2-361LF]
360 kOhm [CR0603-JW-364ELF]	360 mOhm [CRL2010-FW-R360ELF]	360 mOhm [PWR6327WR360JE]	360 Ohm [CAT16-361J4LF]
360 kOhm [CR0805-FX-3603ELF]	360 mOhm [CRL2010-JW-R360ELF]	360 nH [SRP1038A-R36M]	360 Ohm [CAY16-361J4LF]
360 kOhm [CR0805-JW-364ELF]	360 mOhm [CRL2512-FW-R360ELF]	360 nH [SRP1040-R36M]	360 Ohm [CR0402-FX-3600GLF]
360 kOhm [CR1206-FX-3603ELF]	360 mOhm [CRL2512-JW-R360ELF]	360 nH [SRP1045-R36Y]	360 Ohm [CR0402-JW-361GLF]
360 kOhm [CR1206-JW-364ELF]	360 mOhm [CRM1206-FX-R360ELF]	360 nH [SRP1250-R36M]	360 Ohm [CR0603-FX-3600ELF]
360 mOhm [CRL0603-FW-R360ELF]	360 mOhm [PWR1913WR360J]	360 nH [SRP4012TA-R36M]	360 Ohm [CR0603-JW-361ELF]
360 mOhm [CRL0603-JW-R360ELF]	360 mOhm [PWR1913WR360JE]	360 nH [SRP4020-R36M]	360 Ohm [CR0805-FX-3600ELF]
360 mOhm [CRL0805-FW-R360ELF]	360 mOhm [PWR2615WR360J]	360 Ohm [4116R-1-361]	360 Ohm [CR0805-JW-361ELF]
360 mOhm [CRL0805-JW-R360ELF]	360 mOhm [PWR2615WR360JE]	360 Ohm [4116R-1-361LF]	360 Ohm [CR1206-FX-3600ELF]
360 mOhm [CRL1206-FW-R360ELF]	360 mOhm [PWR4525WR360J]	360 Ohm [4310R-101-361]	360 Ohm [CR1206-JW-361ELF]
	360 mOhm [PWR4525WR360JE]	360 Ohm [4608X-102-361LF]	360 Ohm [CR2010-JW-361ELF]
		360 Ohm [4610X-101-361LF]	360 Ohm [PWR163S-25-3600FE]
		360 Ohm [4814P-T01-361]	360 pF [C0402C361K1HACT U]
		360 Ohm [4816P-2-361]	

Multisim 14.1 Education Components

360 pF [C0402C361K3HACT U]	365 kOhm [CR0603-FX- 3653ELF]	37.4 kOhm [CR0805-FX- 3742ELF]	374 Ohm [CR0402- FX-3740GLF]
360 pF [C0402C361K5HACT U]	365 kOhm [CR0805-FX- 3653ELF]	37.4 kOhm [CR1206-FX- 3742ELF]	374 Ohm [CR0603- FX-3740ELF]
360 pF [C0603C361K5GACT U]	365 kOhm [CR1206-FX- 3653ELF]	37.4 kOhm [CRT1206-BY- 3742ELF]	374 Ohm [CR0805- FX-3740ELF]
360 pF [C1206C361KBGAC TU]	365 Ohm [CAY16- 3650F4LF]	37.4 Ohm [CAT16- 37R4F4LF]	374 Ohm [CR1206- FX-3740ELF]
360 pF [C1210C361KBGAC TU]	365 Ohm [CR0402- FX-3650GLF]	37.4 Ohm [CR0402- FX-37R4GLF]	38 Ohm [4116R-1- 380]
360 pF [C1812C361KBGAC TU]	365 Ohm [CR0603- FX-3650ELF]	37.4 Ohm [CR0603- FX-37R4ELF]	38 Ohm [4116R-1- 380LF]
360 pF [C1825C361KBGAC TU]	365 Ohm [CR0805- FX-3650ELF]	37.4 Ohm [CR0805- FX-37R4ELF]	38.3 kOhm [CR0402-FX- 3832GLF]
360 pF [C1825C361KBGAC TU]	365 Ohm [CR1206- FX-3650ELF]	37.4 Ohm [CR0805- FX-37R4GLF]	38.3 kOhm [CR0603-FX- 3832ELF]
360 pF [C2220C361KBGAC TU]	365 Ohm [CRT0402-FZ- 3650GLF]	37.4 Ohm [CR1206- FX-37R4ELF]	38.3 kOhm [CR0805-FX- 3832ELF]
360 pF [C2225C361KBGAC TU]	37.4 kOhm [CR0402-FX- 3742GLF]	374 kOhm [CR0402-FX- 3743GLF]	38.3 kOhm [CR1206-FX- 3832ELF]
3-644456-5	37.4 kOhm [CR0603-FX- 3742ELF]	374 kOhm [CR0603-FX- 3743ELF]	38.3 kOhm [CRT0402-FZ- 3832GLF]
3-644456-8	37.4 kOhm [CR0603-FX- 3742GLF]	374 kOhm [CR0805-FX- 3743ELF]	38.3 kOhm [CRT0603-BY- 3832ELF]
365 kOhm [CR0402-FX- 3653GLF]		374 kOhm [CR1206-FX- 3743ELF]	38.3 kOhm [CRT0805-BY- 3832ELF]

Multisim 14.1 Education Components

38.3 Ohm [CR0402-FX-38R3GLF]	383 Ohm [CR0805-FX-3830ELF]	39 kOhm [4306R-102-393LF]	39 kOhm [4606X-101-393LF]
38.3 Ohm [CR0603-FX-38R3ELF]	383 Ohm [CR1206-FX-3830ELF]	39 kOhm [4308M-102-393]	39 kOhm [4606X-102-393LF]
38.3 Ohm [CR0805-FX-38R3ELF]	383 Ohm [CRM2512-FX-3830ELF]	39 kOhm [4308M-102-393LF]	39 kOhm [4607X-101-393LF]
38.3 Ohm [CR1206-FX-38R3ELF]	383 Ohm [CRT0402-BW-3830GLF]	39 kOhm [4308R-101-393]	39 kOhm [4608M-101-393LF]
38.3 Ohm [CRT0402-FZ-38R3GLF]	39 kOhm [4114R-1-393]	39 kOhm [4308R-101-393LF]	39 kOhm [4608M-102-393LF]
383 kOhm [CR0402-FX-3833GLF]	39 kOhm [4114R-1-393LF]	39 kOhm [4308R-102-393]	39 kOhm [4608X-101-393LF]
383 kOhm [CR0603-FX-3833ELF]	39 kOhm [4116R-1-393]	39 kOhm [4308R-102-393LF]	39 kOhm [4608X-102-393LF]
383 kOhm [CR0805-FX-3833ELF]	39 kOhm [4116R-1-393LF]	39 kOhm [4309R-101-393LF]	39 kOhm [4609H-101-393LF]
383 kOhm [CR0805-FX-3833GLF]	39 kOhm [4116R-2-393]	39 kOhm [4310R-101-393]	39 kOhm [4609X-101-393LF]
383 kOhm [CR0805-FX-3833GLF]	39 kOhm [4116R-2-393LF]	39 kOhm [4310R-101-393LF]	39 kOhm [4610X-101-393LF]
383 kOhm [CR1206-FX-3833ELF]	39 kOhm [4306M-102-393]	39 kOhm [4310R-102-393]	39 kOhm [4610X-102-393LF]
383 kOhm [CRT1206-BY-3833ELF]	39 kOhm [4306M-102-393LF]	39 kOhm [4310R-102-393LF]	39 kOhm [4816P-1-393]
383 Ohm [CR0402-FX-3830GLF]	39 kOhm [4306R-101-393]	39 kOhm [4420P-2-393]	39 kOhm [4816P-1-393LF]
383 Ohm [CR0603-FX-3830ELF]	39 kOhm [4306R-101-393LF]	39 kOhm [4604X-102-393LF]	39 kOhm [4816P-2-393]
		39 kOhm [4606M-102-393LF]	39 kOhm [4816P-2-393LF]

Multisim 14.1 Education Components

39 kOhm [4816P-T01-393]	39 kOhm [CR0201-FW-3902GLF]	39 mOhm [PWR2615WR039F E]	39 nF [C0805C393K4RACT U]
39 kOhm [4816P-T01-393LF]	39 kOhm [CR0402-FX-3902GLF]	39 nF [C0402C393K4RACT U]	39 nF [C0805C393K5RACT U]
39 kOhm [4816P-T02-393]	39 kOhm [CR0603-FX-3902ELF]	39 nF [C0402C393K8RACT U]	39 nF [C0805C393K8RACT U]
39 kOhm [4816P-T02-393LF]	39 kOhm [CR0603-JW-393ELF]	39 nF [C0402C393K9RACT U]	39 nF [C0805F393K1RACT U]
39 kOhm [4820P-2-393F]	39 kOhm [CR0603-JW-393GLF]	39 nF [C0603C393K1RACT U]	39 nF [C0805F393K3RACT U]
39 kOhm [CAT10-393J4LF]	39 kOhm [CR0805-FX-3902ELF]	39 nF [C0603C393K3RACT U]	39 nF [C0805F393K4RACT U]
39 kOhm [CAT16-3902F4LF]	39 kOhm [CR0805-JW-393ELF]	39 nF [C0603C393K4RACT U]	39 nF [C0805F393K5RACT U]
39 kOhm [CAT16-393J4LF]	39 kOhm [CR0805-JW-393GLF]	39 nF [C0603C393K5RACT U]	39 nF [C1206C393K1RACT U]
39 kOhm [CAT25-393JALF]	39 kOhm [CR1206-FX-3902ELF]	39 nF [C0603C393K8RACT U]	39 nF [C1206C393K4RACT U]
39 kOhm [CAY10-393J2LF]	39 kOhm [CR1206-JW-393ELF]	39 nF [C0805C393K1RACT U]	39 nF [C1206C393K5RACT U]
39 kOhm [CAY10-393J4LF]	39 mF [C0805C399KBGAC TU]	39 nF [C0805C393K3RACT U]	39 nF [C1206C393KARACT U]
39 kOhm [CAY16-3902F4LF]	39 mOhm [PWR1913WR039F]		
39 kOhm [CAY16-393J4LF]	39 mOhm [PWR1913WR039F E]		
39 kOhm [CAY16-393J8LF]			
39 kOhm [CAY17-393JALF]			

Multisim 14.1 Education Components

39 nF [C1206C393M1UAC TU]	39 nF [GMC7.3392K63K31 TR12]	39 nF [MDC15393K630B5 3P3TUBE]	39 Ohm [4116R-2- 390]
39 nF [C1210C393K1RACT U]	39 nF [GMC7.3393K63K31 TR12]	39 nF [MDK15393K100B5 3P3TUBE]	39 Ohm [4116R-2- 390LF]
39 nF [C1210C393K2RACT U]	39 nF [MDC10393K100A5 2P3TUBE]	39 nF [MDK15393K400B5 3P3TUBE]	39 Ohm [4306R- 101-390]
39 nF [C1210C393K5RACT U]	39 nF [MDC10393K250A5 2P3TUBE]	39 nF [MDK15393K50B53 P3TUBE]	39 Ohm [4306R- 101-390LF]
39 nF [C1210C393KARACT U]	39 nF [MDC10393K400A5 2P3TUBE]	39 nF [MDS15393K400B5 3P3TUBE]	39 Ohm [4306R- 102-390]
39 nF [C1210C393KARACT U]	39 nF [MDC10393K400A5 2P3TUBE]	39 nF [MDS15393K400B5 3P3TUBE]	39 Ohm [4306R- 102-390LF]
39 nF [C1812C393K1RACT U]	39 nF [MDC10393K50A52 P3TUBE]	39 nF [MDS15393K50B53 P3TUBE]	39 Ohm [4308H- 102-390]
39 nF [C1812C393K5RACT U]	39 nF [MDC10393K630A5 2P3TUBE]	39 nF [MDS15393K630B5 3P3TUBE]	39 Ohm [4308H- 102-390LF]
39 nF [C2220C393K2GACT U]	39 nF [MDC15393K100B5 3P3TUBE]	39 Ohm [4114R-1- 390]	39 Ohm [4308R- 101-390]
39 nF [GMC5.7392K250J3 1TR12]	39 nF [MDC15393K250B5 3P3TUBE]	39 Ohm [4114R-1- 390LF]	39 Ohm [4308R- 102-390LF]
39 nF [GMC5.7393K50J31 TR12]	39 nF [MDC15393K400B5 3P3TUBE]	39 Ohm [4114R-2- 390]	39 Ohm [4308R- 102-390LF]
39 nF [GMC7.3392K250K3 1TR12]	39 nF [MDC15393K50B53 P3TUBE]	39 Ohm [4114R-2- 390LF]	39 Ohm [4310R- 101-390]
		39 Ohm [4116R-1- 390]	39 Ohm [4310R- 101-390LF]
		39 Ohm [4116R-1- 390LF]	39 Ohm [4310R- 102-390]

Multisim 14.1 Education Components

39 Ohm [4310R-102-390LF]	39 Ohm [4610X-101-390LF]	39 Ohm [4816P-T01-390LF]	39 Ohm [CAY17-390JALF]
39 Ohm [4311R-101-390]	39 Ohm [4610X-102-390LF]	39 Ohm [4816P-T02-390]	39 Ohm [CR0201-FW-39R0GLF]
39 Ohm [4416P-1-390]	39 Ohm [4611M-101-390LF]	39 Ohm [4816P-T02-390LF]	39 Ohm [CR0201-JW-390GLF]
39 Ohm [4416P-1-390LF]	39 Ohm [4612X-102-390LF]	39 Ohm [4820P-1-390]	39 Ohm [CR0402-FX-39R0GLF]
39 Ohm [4416P-T01-390]	39 Ohm [4614X-102-390LF]	39 Ohm [4820P-T01-390]	39 Ohm [CR0402-JW-390GLF]
39 Ohm [4420P-1-390]	39 Ohm [4814P-1-390]	39 Ohm [CAT10-390J4LF]	39 Ohm [CR0603-FX-39R0ELF]
39 Ohm [4420P-1-390LF]	39 Ohm [4814P-1-390LF]	39 Ohm [CAT16-390J2LF]	39 Ohm [CR0603-JW-390ELF]
39 Ohm [4420P-T01-390]	39 Ohm [4814P-T01-390]	39 Ohm [CAT16-390J4LF]	39 Ohm [CR0603-JW-390GLF]
39 Ohm [4604M-101-390LF]	39 Ohm [4814P-T01-390LF]	39 Ohm [CAT16-39R0F4LF]	39 Ohm [CR0805-FX-39R0ELF]
39 Ohm [4606M-101-390LF]	39 Ohm [4814P-T02-390]	39 Ohm [CAT25-390JALF]	39 Ohm [CR0805-FX-39R0GLF]
39 Ohm [4606X-101-390LF]	39 Ohm [4816P-1-390]	39 Ohm [CAY10-390J2LF]	39 Ohm [CR0805-JW-390ELF]
39 Ohm [4606X-102-390LF]	39 Ohm [4816P-1-390LF]	39 Ohm [CAY10-390J4LF]	39 Ohm [CR0805-JW-390GLF]
39 Ohm [4608X-101-390LF]	39 Ohm [4816P-2-390]	39 Ohm [CAY16-390J4LF]	39 Ohm [CR1206-FX-39R0ELF]
39 Ohm [4608X-102-390LF]	39 Ohm [4816P-2-390LF]	39 Ohm [CAY16-390J8LF]	39 Ohm [CR1206-JW-390ELF]
39 Ohm [4609X-101-390LF]	39 Ohm [4816P-T01-390]	39 Ohm [CAY16-39R0F4LF]	39 Ohm [CR1206-JW-390GLF]

Multisim 14.1 Education Components

39 Ohm [CR2010-JW-390ELF]	39 pF [C0603C390K5GACT U]	39 pF [C1812C390KBGAC TU]	39 uH [SDR0603-390KL]
39 Ohm [CR2512-JW-390ELF]	39 pF [C0805C390K1GACT U]	39 pF [C1825C390KBGAC TU]	39 uH [SDR0604-390KL]
39 Ohm [CRT0603-DY-39R0ELF]	39 pF [C0805C390K2GACT U]	39 pF [C2220C390KBGAC TU]	39 uH [SDR0703-390KL]
39 Ohm [PWR163S-25-39R0J]	39 pF [C0805C390K5GACT U]	39 pF [C2225C390KBGAC TU]	39 uH [SDR0805-390KL]
39 Ohm [PWR220T-20-39R0F]	39 pF [C0805C390KBGAC TU]	39 uF [16SVPC39MV]	39 uH [SDR0906-390KL]
39 Ohm [PWR220T-20-39R0J]	39 pF [C1206C390K1GACT U]	39 uH [SDE0403A-390K]	39 uH [SDR1006-390KL]
39 Ohm [PWR4318W39R0JE]	39 pF [C1206C390K2GACT U]	39 uH [SDE0604A-390M]	39 uH [SDR1105-390KL]
39 pF [C0201C390K3GACT U]	39 pF [C1206C390K5GACT U]	39 uH [SDE0805A-390M]	39 uH [SDR1307-390KL]
39 pF [C0402C390K4GACT U]	39 pF [C1206C390K8GACT U]	39 uH [SDE1006A-390M]	39 uH [SDR1307A-390K]
39 pF [C0402C390K5GACT U]	39 pF [C1210C390KBGAC TU]	39 uH [SDR0302-390KL]	39 uH [SRP1770TA-390M]
39 pF [C0402C390K8GACT U]	39 pF [C1210C390KBGAC TU]	39 uH [SDR0403-390KL]	39 uH [SRP6540-390M]
39 pF [C0603C390K2GACT U]		39 uH [SDR0503-390KL]	39 uH [SRR0735A-390M]
			39 uH [SRR0745A-390M]
			39 uH [SRR0804-390Y]
			39 uH [SRR0805-390Y]

Multisim 14.1 Education Components

39 uH [SRR0905-390Y]	39 uH [SRR4028-390Y]	39.2 Ohm [CR0603-FX-39R2ELF]	390 kOhm [4308R-101-394LF]
39 uH [SRR0906-390ML]	39 uH [SRR5018-390Y]	39.2 Ohm [CR0603-FX-39R2GLF]	390 kOhm [4308R-102-394]
39 uH [SRR0908-390ML]	39 uH [SRR5028-390Y]	39.2 Ohm [CR0805-FX-39R2ELF]	390 kOhm [4308R-102-394LF]
39 uH [SRR1003-390M]	39 uH [SRR6028-390Y]	39.2 Ohm [CR0805-FX-39R2GLF]	390 kOhm [4310M-101-394]
39 uH [SRR1005-390Y]	39 uH [SRR6038-390Y]	39.2 Ohm [CR1206-FX-39R2ELF]	390 kOhm [4310M-101-394LF]
39 uH [SRR1205-390ML]	39 uH [SRR6040A-390M]	39.2 Ohm [CR2512-FX-39R2ELF]	390 kOhm [4310R-101-394]
39 uH [SRR1206-390YL]	39 uH [SRR7045-390M]	39.2 Ohm [CRM1206-FX-39R2ELF]	390 kOhm [4310R-101-394LF]
39 uH [SRR1208-390YL]	39.2 kOhm [CAY16-3922F4LF]	39.2 Ohm [CRM2512-FX-39R2ELF]	390 kOhm [4310R-102-394]
39 uH [SRR1210-390M]	39.2 kOhm [CR0402-FX-3922GLF]	390 kOhm [4116R-1-394]	390 kOhm [4310R-102-394LF]
39 uH [SRR1210A-390M]	39.2 kOhm [CR0603-FX-3922ELF]	390 kOhm [4116R-1-394LF]	390 kOhm [4604X-102-394LF]
39 uH [SRR1240-390M]	39.2 kOhm [CR0805-FX-3922ELF]	390 kOhm [4116R-2-394]	390 kOhm [4605X-101-394LF]
39 uH [SRR1260-390M]	39.2 kOhm [CR1206-FX-3922ELF]	390 kOhm [4306R-101-394]	390 kOhm [4606X-101-394LF]
39 uH [SRR1260A-390M]	39.2 kOhm [CR1206-FX-3922ELF]	390 kOhm [4306R-101-394LF]	390 kOhm [4606X-102-394LF]
39 uH [SRR1280-390M]	39.2 Ohm [CAY16-39R2F4LF]	390 kOhm [4306R-102-394]	390 kOhm [4608X-101-394LF]
39 uH [SRR4018-390Y]	39.2 Ohm [CR0402-FX-39R2GLF]	390 kOhm [4308R-101-394]	390 kOhm [4608X-102-394LF]

Multisim 14.1 Education Components

390 kOhm [4609M-101-394LF]	390 kOhm [CHV0805-FX-3903ELF]	390 mOhm [CRL0603-JW-R390ELF]	390 nF [C0603C394K4PACT U]
390 kOhm [4610X-101-394LF]	390 kOhm [CR0402-FX-3903GLF]	390 mOhm [CRL0805-FW-R390ELF]	390 nF [C0603C394K4RACT U]
390 kOhm [4610X-102-394LF]	390 kOhm [CR0603-FX-3903ELF]	390 mOhm [CRL0805-JW-R390ELF]	390 nF [C0603C394K8PACT U]
390 kOhm [4814P-1-394]	390 kOhm [CR0603-JW-394ELF]	390 mOhm [CRL1206-FW-R390ELF]	390 nF [C0603C394K8RACT U]
390 kOhm [4816P-1-394]	390 kOhm [CR0603-JW-394GLF]	390 mOhm [CRL1206-JW-R390ELF]	390 nF [C0603C394K9RACT U]
390 kOhm [4816P-T01-394]	390 kOhm [CR0805-FX-3903ELF]	390 mOhm [CRL2010-FW-R390ELF]	390 nF [C0805C394K3RACT U]
390 kOhm [4816P-T01-394LF]	390 kOhm [CR0805-JW-394ELF]	390 mOhm [CRL2010-JW-R390ELF]	390 nF [C0805C394K4RACT U]
390 kOhm [4816P-T02-394]	390 kOhm [CR1206-FX-3903ELF]	390 mOhm [CRL2512-FW-R390ELF]	390 nF [C0805C394K8RACT U]
390 kOhm [CAT16-394J4LF]	390 kOhm [CR1206-JW-394ELF]	390 mOhm [CRL2512-JW-R390ELF]	390 nF [C0805C394K9RACT U]
390 kOhm [CAT25-394JALF]	390 kOhm [CR1206-JW-394GLF]	390 mOhm [CRM2010-FX-R390ELF]	390 nF [C1206C394K1RACT U]
390 kOhm [CAY16-394J4LF]	390 mOhm [CRL0603-FW-R390ELF]	390 mOhm [CRM2512-FX-R390ELF]	390 nF [C1206C394K3RACT U]

Multisim 14.1 Education Components

390 nF [C1206C394K4RACT U]	390 nF [C1812C394K5RACT U]	390 nF [C2225C394K2RACT U]	390 nF [MDK15394K50B53 P3TUBE]
390 nF [C1206C394K5RACT U]	390 nF [C1812C394KARACT U]	390 nF [GMC7.3394K63K37 TR12]	390 nF [MDS15394K50B53 P3TUBE]
390 nF [C1206C394K8RACT U]	390 nF [C1812C394M5UAC TU]	390 nF [MDC10394K100A5 2P3TUBE]	390 nF [MMC12.7394K250 B31TR24]
390 nF [C1206F394K3RACT U]	390 nF [C1812F394K1RACT U]	390 nF [MDC10394K250A5 2P3TUBE]	390 nF [MMC7.3394K50K3 5TR12]
390 nF [C1206F394K4RACT U]	390 nF [C1812F394K2RACT U]	390 nF [MDC10394K400A5 8P7TUBE]	390 nF [MMC7.3394K63K3 5TR12]
390 nF [C1210C394K3RACT U]	390 nF [C1812F394K3RACT U]	390 nF [MDC10394K400A5 8P8TUBE]	390 nH [SRP1038A- R39M]
390 nF [C1210C394K5RACT U]	390 nF [C1812F394K5RACT U]	390 nF [MDC10394K50A52 P3TUBE]	390 nH [SRP1040- R39M]
390 nF [C1210F394K3RACT U]	390 nF [C1825C394K1RACT U]	390 nF [MDC15394K100B5 3P3TUBE]	390 Ohm [4114R-1- 391]
390 nF [C1210F394K4RACT U]	390 nF [C1825C394K2RACT U]	390 nF [MDC15394K250B5 3P3TUBE]	390 Ohm [4114R-1- 391LF]
390 nF [C1210F394K5RACT U]	390 nF [C1825C394K5RACT U]	390 nF [MDC15394K50B53 P3TUBE]	390 Ohm [4114R-2- 391]
390 nF [C1812C394K1RACT U]	390 nF [C2225C394K1RACT U]	390 nF [MDK15394K100B5 3P3TUBE]	390 Ohm [4114R-2- 391LF]
			390 Ohm [4116R-1- 391]
			390 Ohm [4116R-1- 391LF]

Multisim 14.1 Education Components

390 Ohm [4116R-2-391]	390 Ohm [4308R-102-391LF]	390 Ohm [4416P-T02-391]	390 Ohm [4608X-AP2-391LF]
390 Ohm [4116R-2-391LF]	390 Ohm [4309R-101-391]	390 Ohm [4420P-1-391]	390 Ohm [4609X-101-391LF]
390 Ohm [4306H-101-391]	390 Ohm [4309R-101-391LF]	390 Ohm [4420P-T01-391]	390 Ohm [4610M-101-391LF]
390 Ohm [4306H-101-391LF]	390 Ohm [4310H-101-391]	390 Ohm [4420P-T02-391]	390 Ohm [4610X-101-391LF]
390 Ohm [4306M-101-391]	390 Ohm [4310H-101-391LF]	390 Ohm [4604X-102-391LF]	390 Ohm [4610X-102-391LF]
390 Ohm [4306M-101-391LF]	390 Ohm [4310M-101-391]	390 Ohm [4605X-101-391LF]	390 Ohm [4610X-AP2-391LF]
390 Ohm [4306R-101-391]	390 Ohm [4310M-101-391LF]	390 Ohm [4606X-101-391LF]	390 Ohm [4614X-102-391LF]
390 Ohm [4306R-101-391LF]	390 Ohm [4310R-101-391]	390 Ohm [4606X-102-391LF]	390 Ohm [4814P-2-391]
390 Ohm [4306R-102-391]	390 Ohm [4310R-101-391LF]	390 Ohm [4606X-AP1-391LF]	390 Ohm [4814P-2-391LF]
390 Ohm [4306R-102-391LF]	390 Ohm [4310R-102-391]	390 Ohm [4606X-AP2-391LF]	390 Ohm [4814P-T01-391]
390 Ohm [4308H-102-391]	390 Ohm [4310R-102-391LF]	390 Ohm [4607X-101-391LF]	390 Ohm [4814P-T02-391]
390 Ohm [4308M-102-391]	390 Ohm [4311R-101-391]	390 Ohm [4608H-101-391LF]	390 Ohm [4814P-T02-391LF]
390 Ohm [4308R-101-391]	390 Ohm [4311R-101-391LF]	390 Ohm [4608M-102-391LF]	390 Ohm [4816P-1-391]
390 Ohm [4308R-101-391LF]	390 Ohm [4416P-2-391]	390 Ohm [4608X-101-391LF]	390 Ohm [4816P-1-391LF]
390 Ohm [4308R-102-391]	390 Ohm [4416P-T01-391]	390 Ohm [4608X-102-391LF]	390 Ohm [4816P-2-391]

Multisim 14.1 Education Components

390 Ohm [4816P-2-391LF]	390 Ohm [CR0402-JW-391GLF]	390 Ohm [PWR4318W3900FE]	390 pF [C0603C391K2RACTU]
390 Ohm [4816P-T01-391]	390 Ohm [CR0603-FX-3900ELF]	390 Ohm [PWR4318W3900JE]	390 pF [C0603C391K3GACTU]
390 Ohm [4816P-T01-391LF]	390 Ohm [CR0603-FX-3900GLF]	390 Ohm [PWR4525W3900JE]	390 pF [C0603C391K3RACTU]
390 Ohm [4816P-T02-391]	390 Ohm [CR0603-JW-391ELF]	390 Ohm [PWR5322W3900JE]	390 pF [C0603C391K4RACTU]
390 Ohm [4816P-T02-391LF]	390 Ohm [CR0805-FX-3900ELF]	390 pF [C0402C391K1HACTU]	390 pF [C0603C391K5GACTU]
390 Ohm [4820P-2-391]	390 Ohm [CR0805-FX-3900GLF]	390 pF [C0402C391K3HACTU]	390 pF [C0603C391K5RACTU]
390 Ohm [4820P-T01-391]	390 Ohm [CR1206-FX-3900ELF]	390 pF [C0402C391K3RACTU]	390 pF [C0805C391K1GACTU]
390 Ohm [4820P-T02-391]	390 Ohm [CR1206-JW-391ELF]	390 pF [C0402C391K4RACTU]	390 pF [C0805C391K2GACTU]
390 Ohm [CAT16-391J4LF]	390 Ohm [CR1206-JW-391GLF]	390 pF [C0402C391K5HACTU]	390 pF [C0805C391K4RACTU]
390 Ohm [CAT25-391JALF]	390 Ohm [CR2010-JW-391ELF]	390 pF [C0603C391K1RACTU]	
390 Ohm [CAY10-391J4LF]	390 Ohm [CR2512-JW-391ELF]		
390 Ohm [CAY16-3900F4LF]	390 Ohm [CRM2512-FX-3900ELF]	390 pF [C0402C391K5RACTU]	
390 Ohm [CAY16-391J4LF]	390 Ohm [PWR263S-35-3900FE]		
390 Ohm [CAY16-391J8LF]			
390 Ohm [CR0402-FX-3900GLF]			

Multisim 14.1 Education Components

390 pF [C0805C391K5RACT U]	390 pF [CA064C391K5GAC TU]	390 uH [SDE0805A- 391K]	390 uH [SRR0804- 391K]
390 pF [C1206C391K1GACT U]	390 uF [2R5SVPC390MV]	390 uH [SDE1006A- 391K]	390 uH [SRR0905- 391K]
390 pF [C1206C391K2GACT U]	390 uF [2SEPC390M]	390 uH [SDR0302- 391KL]	390 uH [SRR0906- 391YL]
390 pF [C1206C391K5GACT U]	390 uF [6SVPC390M]	390 uH [SDR0403- 391KL]	390 uH [SRR0908- 391YL]
390 pF [C1206C391K5GACT U]	390 uF [A700X397M002AT E010]	390 uH [SDR0503- 391KL]	390 uH [SRR1003- 391Y]
390 pF [C1206C391KBGAC TU]	390 uF [A700X397M002AT E015]	390 uH [SDR0603- 391KL]	390 uH [SRR1005- 391K]
390 pF [C1206C391KCGAC TU]	390 uF [EEFCX0D391R]	390 uH [SDR0604- 391KL]	390 uH [SRR1205- 391KL]
390 pF [C1210C391KBGAC TU]	390 uF [EEFCX0E391R]	390 uH [SDR0703- 391KL]	390 uH [SRR1206- 391KL]
390 pF [C1812C391KBGAC TU]	390 uF [EEFSX0D391E4]	390 uH [SDR0805- 391KL]	390 uH [SRR1208- 391KL]
390 pF [C1825C391KBGAC TU]	390 uF [EEFSX0D391ER]	390 uH [SDR0906- 391KL]	390 uH [SRR1210- 391M]
390 pF [C2220C391KBGAC TU]	390 uF [EEFSX0E391E4]	390 uH [SDR1006- 391KL]	390 uH [SRR1210A- 391M]
390 pF [C2225C391KBGAC TU]	390 uF [EEFSX0E391XE]	390 uH [SDR1307- 391KL]	390 uH [SRR1240- 391K]
	390 uF [EEFSX0E391ER]	390 uH [SDR1307A-391K]	390 uH [SRR1260- 391K]
	390 uF [EEFSX0E391ER]	390 uH [SRR0735A- 391M]	390 uH [SRR1260A- 391K]
	390 uF [EEFSX0E391XE]	390 uH [SRR0745A- 391M]	390 uH [SRR1280- 391K]

Multisim 14.1 Education Components

390 uH [SRR4028-391Y]	392 Ohm [CRT1206-BY-3920ELF]	3LP01SS-TL-E	3PST_SB
390 uH [SRR7045-391M]	3BH41	3LP01SS-TL-H	4 kOhm [4116R-1-402]
392 kOhm [CR0201-FW-3923GLF]	3GH41	3LP01S-TL-E	4 kOhm [4116R-1-402LF]
392 kOhm [CR0402-FX-3923GLF]	3JH41	3N246	4 kOhm [CR1206-FX-4001ELF]
392 kOhm [CR0603-FX-3923ELF]	3KASMC15AHE3/57T	3N247	4 mOhm [CRA2512-FZ-R004ELF]
392 kOhm [CR0805-FX-3923ELF]	3KASMC17AHM3_A/H	3N248	4 mOhm [CRE2512-FZ-R004E-2]
392 kOhm [CR1206-FX-3923ELF]	3KASMC24AHE3/9AT	3N249	4 mOhm [CRE2512-FZ-R004E-3]
392 Ohm [4816P-1-3920F]	3KASMC28AHM3/57T	3N250	4 mOhm [CRF2512-FX-R004ELF]
392 Ohm [CR0402-FX-3920GLF]	3Line_Bussed	3N251	4 Ohm [PWR163S-25-4R00FE]
392 Ohm [CR0603-FX-3920ELF]	3Line_Isolated	3N252	4 Ohm [PWR163S-25-4R00JE]
392 Ohm [CR0805-FX-3920ELF]	3LN01C-TB-E	3N253	4 Ohm [PWR220T-35-4R00F]
392 Ohm [CR1206-FX-3920ELF]	3LN01C-TB-H	3N254	4 Ohm [PWR221T-30-4R00F]
392 Ohm [CRM1206-FX-3920ELF]	3LN01M-TL-E	3N255	4 Ohm [PWR263S-35-4R00F]
	3LN01M-TL-H	3N256	4 Ohm [PWR263S-35-4R00JE]
	3LN01SS-TL-E	3N257	4.02 kOhm [CR0402-FX-4021GLF]
	3LN01SS-TL-H	3N258	
	3LN01S-TL-E	3N259	
	3LP01C-TB-E	3P1S	
	3LP01C-TB-H	3P2S	
	3LP01M-TL-E	3P3S	
	3LP01M-TL-H	3P4S	
		3P5S	
		3PDT_DB	
		3PDT_SB	
		3PST_DB	

Multisim 14.1 Education Components

4.02 kOhm [CR0603-FX-4021ELF]	4.12 kOhm [CR1206-FX-4121ELF]	4.3 kOhm [CR0603-FX-4301ELF]	4.3 nF [C0603C432K5HACTU]
4.02 kOhm [CR0805-FX-4021ELF]	4.2 uH [SRP1205-4R0Y]	4.3 kOhm [CR0603-JW-432ELF]	4.3 nF [C0805C432K1GACTU]
4.02 kOhm [CR1206-FX-4021ELF]	4.2 uH [SRR5028-4R2Y]	4.3 kOhm [CR0805-FX-4301ELF]	4.3 nF [C0805C432K1HACTU]
4.02 kOhm [CRT0402-FZ-4021GLF]	4.22 kOhm [CR0402-FX-4221GLF]	4.3 kOhm [CR0805-JW-432ELF]	4.3 nF [C0805C432K3HACTU]
4.02 kOhm [CRT0603-BY-4021ELF]	4.22 kOhm [CR0603-FX-4221ELF]	4.3 kOhm [CR1206-JW-432ELF]	4.3 nF [C0805C432K5HACTU]
4.02 kOhm [CRT0805-BY-4021ELF]	4.22 kOhm [CR0805-FX-4221ELF]	4.3 kOhm [PWR163S-25-4301FE]	4.3 nF [C1825C432KBGAC TU]
4.02 MOhm [CR1206-FW-4024ELF]	4.22 kOhm [CR1206-FX-4221ELF]	4.3 MOhm [4308R-102-435]	4.3 nF [C2220C432KBGAC TU]
4.1 uH [SRR5018-4R1Y]	4.22 kOhm [CR2010-FX-4221ELF]	4.3 MOhm [CR0603-JW-435ELF]	4.3 nF [C2225C432KBGAC TU]
4.12 kOhm [CAY16-4121F4LF]	4.3 kOhm [4308R-102-432]	4.3 MOhm [CR0805-JW-435ELF]	4.3 Ohm [CR0402-J/-4R3GLF]
4.12 kOhm [CR0402-FX-4121GLF]	4.3 kOhm [CAY10-432J4LF]	4.3 MOhm [CR1206-JW-435ELF]	4.3 Ohm [CR0603-J/-4R3ELF]
4.12 kOhm [CR0603-FX-4121ELF]	4.3 kOhm [CAY16-432J4LF]	4.3 nF [C0603C432K1HACTU]	4.3 Ohm [CR0603-J/-4R3GLF]
4.12 kOhm [CR0805-FX-4121ELF]	4.3 kOhm [CR0402-FX-4301GLF]	4.3 nF [C0603C432K3HACTU]	4.3 Ohm [CR0805-J/-4R3ELF]

Multisim 14.1 Education Components

4.3 Ohm [CR1206-J/-4R3ELF]	4.32 kOhm [CR0805-FX-4321ELF]	4.5 Ohm [PWR220T-35-4R50F]	4.6 uH [SDR1305-4R6Y]
4.3 Ohm [CRL0603-FW-4R30ELF]	4.32 kOhm [CR0805-FX-4321GLF]	4.5 uH [SDR1045-4R5M]	4.64 kOhm [CR0402-FX-4641GLF]
4.3 Ohm [CRL0603-JW-4R30ELF]	4.32 kOhm [CR1206-FX-4321ELF]	4.5 uH [SRR1208-4R5ML]	4.64 kOhm [CR0603-FX-4641ELF]
4.3 Ohm [CRL0805-FW-4R30ELF]	4.4 uH [SRU2009-4R4Y]	4.5 uH [SRR1280-4R5Y]	4.64 kOhm [CR0805-FX-4641ELF]
4.3 Ohm [CRL0805-JW-4R30ELF]	4.42 kOhm [CR0402-FX-4421GLF]	4.53 kOhm [CAY16-4531F4LF]	4.64 kOhm [CR1206-FX-4641ELF]
4.3 Ohm [CRL1206-FW-4R30ELF]	4.42 kOhm [CR0603-FX-4421ELF]	4.53 kOhm [CR0201-FW-4531GLF]	4.64 kOhm [CR2512-FX-4641ELF]
4.3 Ohm [CRL1206-JW-4R30ELF]	4.42 kOhm [CR0805-FX-4421ELF]	4.53 kOhm [CR0603-FX-4531ELF]	4.64 kOhm [CRT0402-FZ-4641GLF]
4.3 Ohm [CRL2010-FW-4R30ELF]	4.42 kOhm [CR1206-FX-4421ELF]	4.53 kOhm [CR0805-FX-4531ELF]	4.64 kOhm [CRT0603-BY-4641ELF]
4.3 Ohm [CRL2010-JW-4R30ELF]	4.42 kOhm [CRT0603-BY-4421ELF]	4.53 kOhm [CR1206-FX-4531ELF]	4.7 kOhm [4108R-1-472]
4.3 Ohm [CRL2512-FW-4R30ELF]	4.42 kOhm [CRT0805-BX-4421ELF]	4.53 kOhm [CRT0603-FX-4531ELF]	4.7 kOhm [4108R-1-472LF]
4.3 Ohm [CRM2512-FX-4R30ELF]	4.42 MOhm [CR1206-FW-4424ELF]	4.53 kOhm [CRT0805-BY-4531ELF]	4.7 kOhm [4114R-1-472]
4.32 kOhm [CAY16-4321F4LF]			4.7 kOhm [4114R-1-472LF]
4.32 kOhm [CR0402-FX-4321GLF]			
4.32 kOhm [CR0603-FX-4321ELF]			

Multisim 14.1 Education Components

4.7 kOhm [4114R-2-472]	4.7 kOhm [4306R-101-472LF]	4.7 kOhm [4309R-101-472]	4.7 kOhm [4416P-1-472LF]
4.7 kOhm [4114R-2-472LF]	4.7 kOhm [4306R-102-472]	4.7 kOhm [4309R-101-472LF]	4.7 kOhm [4416P-2-472]
4.7 kOhm [4116R-1-472]	4.7 kOhm [4306R-102-472LF]	4.7 kOhm [4310H-101-472]	4.7 kOhm [4416P-2-472LF]
4.7 kOhm [4116R-1-472LF]	4.7 kOhm [4308H-101-472]	4.7 kOhm [4310H-101-472LF]	4.7 kOhm [4416P-T01-472]
4.7 kOhm [4116R-2-472]	4.7 kOhm [4308H-101-472LF]	4.7 kOhm [4310H-102-472]	4.7 kOhm [4416P-T02-472]
4.7 kOhm [4116R-2-472LF]	4.7 kOhm [4308H-102-472]	4.7 kOhm [4310H-102-472LF]	4.7 kOhm [4416P-T02-472LF]
4.7 kOhm [4304M-101-472]	4.7 kOhm [4308H-102-472LF]	4.7 kOhm [4310M-101-472]	4.7 kOhm [4420P-1-472]
4.7 kOhm [4304M-101-472LF]	4.7 kOhm [4308M-101-472]	4.7 kOhm [4310M-101-472LF]	4.7 kOhm [4420P-1-472LF]
4.7 kOhm [4306H-101-472]	4.7 kOhm [4308M-101-472LF]	4.7 kOhm [4310R-101-472]	4.7 kOhm [4420P-2-472]
4.7 kOhm [4306H-101-472LF]	4.7 kOhm [4308M-102-472]	4.7 kOhm [4310R-101-472LF]	4.7 kOhm [4420P-2-472LF]
4.7 kOhm [4306H-102-472]	4.7 kOhm [4308M-102-472LF]	4.7 kOhm [4310R-102-472]	4.7 kOhm [4420P-T01-472]
4.7 kOhm [4306M-101-472]	4.7 kOhm [4308R-101-472]	4.7 kOhm [4310R-102-472LF]	4.7 kOhm [4420P-T01-472LF]
4.7 kOhm [4306M-101-472LF]	4.7 kOhm [4308R-101-472LF]	4.7 kOhm [4311R-101-472]	4.7 kOhm [4420P-T02-472]
4.7 kOhm [4306M-102-472]	4.7 kOhm [4308R-102-472]	4.7 kOhm [4311R-101-472LF]	4.7 kOhm [4420P-T02-472LF]
4.7 kOhm [4306R-101-472]	4.7 kOhm [4308R-102-472LF]	4.7 kOhm [4416P-1-472]	4.7 kOhm [4604H-101-472LF]

Multisim 14.1 Education Components

4.7 kOhm [4604X-101-472LF]	4.7 kOhm [4608H-102-472LF]	4.7 kOhm [4610X-101-472LF]	4.7 kOhm [4814P-T01-472LF]
4.7 kOhm [4604X-102-472LF]	4.7 kOhm [4608M-101-472LF]	4.7 kOhm [4610X-102-472LF]	4.7 kOhm [4814P-T02-472]
4.7 kOhm [4605H-101-472LF]	4.7 kOhm [4608M-102-472LF]	4.7 kOhm [4610X-AP1-472LF]	4.7 kOhm [4814P-T02-472LF]
4.7 kOhm [4605M-101-472LF]	4.7 kOhm [4608X-101-472LF]	4.7 kOhm [4610X-AP2-472LF]	4.7 kOhm [4816P-1-472]
4.7 kOhm [4605X-101-472LF]	4.7 kOhm [4608X-102-472LF]	4.7 kOhm [4611X-101-472LF]	4.7 kOhm [4816P-1-472F]
4.7 kOhm [4605X-AP1-472LF]	4.7 kOhm [4608X-AP1-472LF]	4.7 kOhm [4612X-101-472LF]	4.7 kOhm [4816P-1-472LF]
4.7 kOhm [4606H-101-472LF]	4.7 kOhm [4608X-AP2-472LF]	4.7 kOhm [4612X-102-472LF]	4.7 kOhm [4816P-2-472]
4.7 kOhm [4606H-102-472LF]	4.7 kOhm [4609H-101-472LF]	4.7 kOhm [4613X-101-472LF]	4.7 kOhm [4816P-2-472F]
4.7 kOhm [4606M-101-472LF]	4.7 kOhm [4609M-101-472LF]	4.7 kOhm [4614X-101-472LF]	4.7 kOhm [4816P-2-472LF]
4.7 kOhm [4606X-101-472LF]	4.7 kOhm [4609X-101-472LF]	4.7 kOhm [4614X-102-472LF]	4.7 kOhm [4816P-T01-472]
4.7 kOhm [4606X-102-472LF]	4.7 kOhm [4609X-AP1-472LF]	4.7 kOhm [4814P-1-472]	4.7 kOhm [4816P-T01-472LF]
4.7 kOhm [4606X-AP1-472LF]	4.7 kOhm [4610H-101-472LF]	4.7 kOhm [4814P-1-472LF]	4.7 kOhm [4816P-T02-472]
4.7 kOhm [4606X-AP2-472LF]	4.7 kOhm [4610H-102-472LF]	4.7 kOhm [4814P-2-472]	4.7 kOhm [4816P-T02-472LF]
4.7 kOhm [4607X-101-472LF]	4.7 kOhm [4610M-101-472LF]	4.7 kOhm [4814P-2-472LF]	4.7 kOhm [4818P-2-472]
4.7 kOhm [4608H-101-472LF]	4.7 kOhm [4610M-102-472LF]	4.7 kOhm [4814P-T01-472]	4.7 kOhm [4818P-2-472LF]

Multisim 14.1 Education Components

4.7 kOhm [4818P-T02-472]	4.7 kOhm [CAT16-472J8LF]	4.7 kOhm [CR0603-JW-472ELF]	4.7 kOhm [CRS2010-FX-4701ELF]
4.7 kOhm [4820P-1-472]	4.7 kOhm [CAT25-472JALF]	4.7 kOhm [CR0603-JW-472GLF]	4.7 kOhm [CRT0402-FZ-4701GLF]
4.7 kOhm [4820P-1-472F]	4.7 kOhm [CAY10-472J2LF]	4.7 kOhm [CR0805-FX-4701ELF]	4.7 kOhm [CRT0603-FX-4701ELF]
4.7 kOhm [4820P-1-472LF]	4.7 kOhm [CAY10-472J4LF]	4.7 kOhm [CR0805-FX-4701GLF]	4.7 kOhm [CRT0805-BY-4701ELF]
4.7 kOhm [4820P-2-472]	4.7 kOhm [CAY16-4701F4LF]	4.7 kOhm [CR0805-JW-472ELF]	4.7 kOhm [PWR4525W4701J]
4.7 kOhm [4820P-2-472F]	4.7 kOhm [CAY16-472J2LF]	4.7 kOhm [CR0805-JW-472GLF]	4.7 kOhm [PWR4525W4701JE]
4.7 kOhm [4820P-2-472LF]	4.7 kOhm [CAY16-472J4GLF]	4.7 kOhm [CR1206-FX-4701ELF]	4.7 kOhm [PWR6327W4701J]
4.7 kOhm [4820P-T01-472]	4.7 kOhm [CAY16-472J4LF]	4.7 kOhm [CR1206-JW-472ELF]	4.7 kOhm [PWR6327W4701JE]
4.7 kOhm [4820P-T01-472LF]	4.7 kOhm [CAY16-472J8LF]	4.7 kOhm [CR1206-JW-472GLF]	4.7 kOhm [PWR6327W4701JE]
4.7 kOhm [4820P-T02-472]	4.7 kOhm [CAY17-472JALF]	4.7 kOhm [CR2512-JW-472ELF]	4.7 mH [SDR0503-472JL]
4.7 kOhm [4820P-T02-472LF]	4.7 kOhm [CR0201-FW-4701GLF]	4.7 kOhm [CRM1206-JW-472ELF]	4.7 mH [SDR0805-472KL]
4.7 kOhm [CAT10-472J4LF]	4.7 kOhm [CR0201-JW-472GLF]	4.7 kOhm [CRM2010-JW-472ELF]	4.7 mH [SDR0906-472KL]
4.7 kOhm [CAT16-4701F4LF]	4.7 kOhm [CR0402-FX-4701GLF]	4.7 kOhm [CRM2512-FX-4701ELF]	4.7 mH [SDR1005-472KL]
4.7 kOhm [CAT16-472J2LF]	4.7 kOhm [CR0402-JW-472GLF]	4.7 kOhm [CRS1206-FX-4701ELF]	4.7 mH [SDR1006-472KL]
4.7 kOhm [CAT16-472J4LF]	4.7 kOhm [CR0603-FX-4701ELF]		

Multisim 14.1 Education Components

4.7 mH [SRE6603-472M]	4.7 MOhm [CR0402-JW-475GLF]	4.7 nF [C0402C472K4RACTU]	4.7 nF [C0603C472K5RACTU]
4.7 mH [SRR0906-472YL]	4.7 MOhm [CR0603-JW-475ELF]	4.7 nF [C0402C472K5RACTU]	4.7 nF [C0603C472K8RACTU]
4.7 mH [SRR0908-472YL]	4.7 MOhm [CR0805-FX-4704ELF]	4.7 nF [C0402C472K8RACTU]	4.7 nF [C0603C472K9RACTU]
4.7 mH [SRR1208-472KL]	4.7 MOhm [CR0805-JW-475ELF]	4.7 nF [C0402C472K9RACTU]	4.7 nF [C0805C472K1GACTU]
4.7 mH [SRR6603-472ML]	4.7 MOhm [CR1206-FW-4704ELF]	4.7 nF [C0603C472K1HACTU]	4.7 nF [C0805C472K1HACTU]
4.7 MOhm [4310R-101-475]	4.7 MOhm [CR1206-JW-475ELF]	4.7 nF [C0603C472K1RACTU]	4.7 nF [C0805C472K1RACTU]
4.7 MOhm [4310R-101-475LF]	4.7 nF [03063C472KAT2A]	4.7 nF [C0603C472K3GACTU]	4.7 nF [C0805C472K2RACTU]
4.7 MOhm [4604X-102-475LF]	4.7 nF [03066C472KAT2A]	4.7 nF [C0603C472K3HACTU]	4.7 nF [C0805C472K3GACTU]
4.7 MOhm [4608X-102-475LF]	4.7 nF [0306YC472KAT2A]	4.7 nF [C0603C472K3RACTU]	4.7 nF [C0805C472K3HACTU]
4.7 MOhm [CAT25-475JALF]	4.7 nF [05085C472KAT2V]	4.7 nF [C0603C472K4RACTU]	4.7 nF [C0805C472K3RACTU]
4.7 MOhm [CAY16-4704F4LF]	4.7 nF [06123C472KAT2S]	4.7 nF [C0603C472K5HACTU]	4.7 nF [C0805C472K4RACTU]
4.7 MOhm [CHV0603-JW-475ELF]	4.7 nF [C0402C472K3RACTU]		
4.7 MOhm [CHV2010-JW-475ELF]			
4.7 MOhm [CR0402-FX-4704GLF]			

Multisim 14.1 Education Components

4.7 nF [C0805C472K5HACT U]	4.7 nF [C1210C472K2RACT U]	4.7 nF [CA064C472K3RACT U]	4.7 nF [GPC7.3472K63K31 TR12]
4.7 nF [C0805C472K5RACT U]	4.7 nF [C1210C472K5GACT U]	4.7 nF [CA064C472K5RACT U]	4.7 nF [MMC5.7472K100J 31TR12]
4.7 nF [C0805C472KARACT U]	4.7 nF [C1210C472K5RACT U]	4.7 nF [GMC5.7472K100J3 1TR12]	4.7 nF [MMC5.7472K250J 31TR12]
4.7 nF [C1206C472K1RACT U]	4.7 nF [C1812C472K1GACT U]	4.7 nF [GMC5.7472K50J31 TR12]	4.7 nF [MMC5.7472K50J3 1TR12]
4.7 nF [C1206C472K2RACT U]	4.7 nF [C1812C472K2GACT U]	4.7 nF [GMC5.7473K100J3 5TR12]	4.7 nF [MMC7.3472K100K 31TR12]
4.7 nF [C1206C472K3RACT U]	4.7 nF [C1812C472K5GACT U]	4.7 nF [GMC7.3472K100K3 1TR12]	4.7 nF [MMC7.3472K250K 31TR12]
4.7 nF [C1206C472K4GACT U]	4.7 nF [C1825C472K2GACT U]	4.7 nF [GMC7.3472K400K3 1TR12]	4.7 nF [MMC7.3472K400K 31TR12]
4.7 nF [C1206C472K5GACT U]	4.7 nF [C1825C472KBGAC TU]	4.7 nF [GMC7.3473K100K3 1TR12]	4.7 nF [MMC7.3472K50K3 1TR12]
4.7 nF [C1206C472K5RACT U]	4.7 nF [C2220C472KBGAC TU]	4.7 nF [GMC7.3473K250K3 7TR12]	4.7 nF [MMC7.3472K63K3 1TR12]
4.7 nF [C1210C472K1GACT U]	4.7 nF [C2225C472K2GACT U]	4.7 nF [GPC7.3471K630K3 1TR12]	4.7 nF [SPC7.3472K100K31 TR12]
4.7 nF [C1210C472K1RACT U]	4.7 nF [C2225C472KBGAC TU]	4.7 nF [GPC7.3472K160K3 1TR12]	4.7 nF [SPC7.3472K250K31 TR12]

Multisim 14.1 Education Components

4.7 nF [SPC7.3472K400K35 TR12]	4.7 Ohm [CRL0805- JW-4R70ELF]	4.7 Ohm [CRS2512- JW-4R7ELF]	4.7 Ohm [PWR220T-20- 4R70F]
4.7 nF [SPC7.3472K630K37 TR12]	4.7 Ohm [CRL1206- FW-4R70ELF]	4.7 Ohm [CRT0805- BW-4R70ELF]	4.7 Ohm [PWR220T-20- 4R70J]
4.7 nF [W2F15C4728AT1A]	4.7 Ohm [CRL1206- JW-4R70ELF]	4.7 Ohm [CRT0805- BY-4R70ELF]	4.7 Ohm [PWR220T-35- 4R70F]
4.7 nF [W3F15C4728AT1A]	4.7 Ohm [CRL2010- JW-4R70ELF]	4.7 Ohm [FW10A4R70JA]	4.7 Ohm [PWR220T-35- 4R70J]
4.7 Ohm [CR0402- J/-4R7GLF]	4.7 Ohm [CRL2512- FW-4R70ELF]	4.7 Ohm [FW20A4R70JA]	4.7 Ohm [PWR221T-30- 4R70F]
4.7 Ohm [CR0603- J/-4R7ELF]	4.7 Ohm [CRM0805-JW- 4R7ELF]	4.7 Ohm [FW30A4R70JA]	4.7 Ohm [PWR221T-30- 4R70J]
4.7 Ohm [CR0805- J/-4R7ELF]	4.7 Ohm [CRM1206-JW- 4R7ELF]	4.7 Ohm [FW50A4R70JA]	4.7 Ohm [PWR221T-30- 4R70J]
4.7 Ohm [CR0805- J/-4R7GLF]	4.7 Ohm [CRM2010-FX- 4R70ELF]	4.7 Ohm [FW70A4R70JA]	4.7 Ohm [PWR2615W4R70F]
4.7 Ohm [CR1206- J/-4R7ELF]	4.7 Ohm [CRM2010-JW- 4R7ELF]	4.7 Ohm [PWR163S-25- 4R70F]	4.7 Ohm [PWR2615W4R70F E]
4.7 Ohm [CR2010- J/-4R7ELF]	4.7 Ohm [CRM2512-FX- 4R70ELF]	4.7 Ohm [PWR163S-25- 4R70J]	4.7 Ohm [PWR2615W4R70J]
4.7 Ohm [CR2512- J/-4R7ELF]	4.7 Ohm [CRM2512-JW- 4R7ELF]	4.7 Ohm [PWR1913W4R70J]	4.7 Ohm [PWR2615W4R70JE]
4.7 Ohm [CRL0603- FW-4R70ELF]	4.7 Ohm [CRS2010- JW-4R7ELF]	4.7 Ohm [PWR2010W4R70JE]	4.7 Ohm [PWR263S-20- 4R70F]
4.7 Ohm [CRL0603- JW-4R70ELF]			4.7 Ohm [PWR263S-20- 4R70J]

Multisim 14.1 Education Components

4.7 Ohm [PWR263S-20-4R70JE]	4.7 uF [C0603C475K9PACTU]	4.7 uF [C1206C475K8PACTU]	4.7 uF [C1210C475K8PACTU]
4.7 Ohm [PWR263S-35-4R70F]	4.7 uF [C0805C475K3PACTU]	4.7 uF [C1206C475K8RACTU]	4.7 uF [C1210C475K8RACTU]
4.7 Ohm [PWR263S-35-4R70FE]	4.7 uF [C0805C475K4PACTU]	4.7 uF [C1206C475K9PACTU]	4.7 uF [C1210C475K9PACTU]
4.7 Ohm [PWR263S-35-4R70J]	4.7 uF [C0805C475K8PACTU]	4.7 uF [C1206C475K9RACTU]	4.7 uF [C1210C475K9RACTU]
4.7 Ohm [PWR3014WA4R70JE]	4.7 uF [C0805C475K9PACTU]	4.7 uF [C1210C475K3NAC TU]	4.7 uF [C1210C475M4VAC TU]
4.7 Ohm [PWR4318W4R70JE]	4.7 uF [C1206C475K3PACTU]	4.7 uF [C1210C475K3PACTU]	4.7 uF [C1210C475M8VAC TU]
4.7 Ohm [PWR5322W4R70J]	4.7 uF [C1206C475K3RACTU]	4.7 uF [C1210C475K3RACTU]	4.7 uF [MDC10475K100A5 3P3TR32]
4.7 Ohm [PWR5322W4R70JE]	4.7 uF [C1206C475K4PACTU]	4.7 uF [C1210C475K4PACTU]	4.7 uF [MDC10475K100A5 3P4TR32]
4.7 Ohm [PWR6327N4R70JE]	4.7 uF [C1206C475K4RACTU]	4.7 uF [C1210C475K4RACTU]	4.7 uF [MDC10475K100A5 4P3TUBE]
4.7 Ohm [PWR6327W4R70JE]	4.7 uF [C1206C475K5PACTU]	4.7 uF [C1210C475K5R1C7 186]	4.7 uF [MDC10475K100A5 4P4TUBE]
4.7 uF [10TPU4R7MSI]	4.7 uF [C1206C475K8NAC TU]	4.7 uF [C1210C475K5RACTU]	4.7 uF [MDC10475K50A52 P3TUBE]

Multisim 14.1 Education Components

4.7 uF [MDC15475K100B5 3P3TUBE]	4.7 uF [T491B475M010AT]	4.7 uF [T494A475M016AT]	4.7 uF [T495A475M010AT E1K3]
4.7 uF [MDC15475K50B53 P3TUBE]	4.7 uF [T491B475M016AT]	4.7 uF [T494A475M020AT]	4.7 uF [T495B475M016AT E700]
4.7 uF [MDK10475K50A52 P3TUBE]	4.7 uF [T491B475M020AT]	4.7 uF [T494A475M025AT]	4.7 uF [T495C475M035AT E450]
4.7 uF [MDK15475K50B53 P3TUBE]	4.7 uF [T491C475M025AT]	4.7 uF [T494B475M010AT]	4.7 uF [T495C475M035AT E500]
4.7 uF [MDS10475K50A52 P3TUBE]	4.7 uF [T491C475M020AT]	4.7 uF [T494B475M016AT]	4.7 uF [T495C475M035AT E500]
4.7 uF [T409D475M010AH 4250]	4.7 uF [T491C475M025AT]	4.7 uF [T494B475M020AT]	4.7 uF [T495C475M035AT E600]
4.7 uF [T429C475M006AH 4250]	4.7 uF [T491C475M035AT]	4.7 uF [T494B475M025AT]	4.7 uF [T495D475M050AT E275]
4.7 uF [T491A475M004AT]	4.7 uF [T491D475M035AT]	4.7 uF [T494C475M020AT]	4.7 uF [T495D475M050AT E300]
4.7 uF [T491A475M006AT]	4.7 uF [T491D475M050AT]	4.7 uF [T494C475M025AT]	4.7 uF [T495D475M050AT E300]
4.7 uF [T491A475M010AT]	4.7 uF [T491S475M006AT]	4.7 uF [T494C475M035AT]	4.7 uF [T495X475M050AT E300]
4.7 uF [T491A475M016AT]	4.7 uF [T491S475M010AT]	4.7 uF [T494D475M035AT]	4.7 uF [T498A475M010AT E2K9]
4.7 uF [T491A475M020AT]	4.7 uF [T491T475M016AT]	4.7 uF [T494D475M050AT]	4.7 uF [T498B475M010AT E2K7]
4.7 uF [T491A475M025AT]	4.7 uF [T494A475M004AT]	4.7 uF [T494S475M006AT]	4.7 uF [T498B475M016AT E2K1]
	4.7 uF [T494A475M006AT]	4.7 uF [T494S475M010AT]	
	4.7 uF [T494A475M010AT]	4.7 uF [T494T475M016AT]	

Multisim 14.1 Education Components

4.7 uF [T521D475M063AT E075]	4.7 uF [TAJB475K025RNJ]	4.7 uF [TAJS475K006RNJ]	4.7 uF [TPSA475K020R180 0]
4.7 uF [T521D475M063AT E300]	4.7 uF [TAJB475K035RNJ]	4.7 uF [TAJS475K010RNJ]	4.7 uF [TPSB475K016R080 0]
4.7 uF [T540D475M063AH 6510]	4.7 uF [TAJC475K020RNJ]	4.7 uF [TAJS475K016RNJ]	4.7 uF [TPSB475K016R150 0]
4.7 uF [TACL475K004RTA]	4.7 uF [TAJC475K035RNJ]	4.7 uF [TAJT475K010RNJ]	4.7 uF [TPSB475K020R100 0]
4.7 uF [TACL475K006RTA]	4.7 uF [TAJC475K050RNJ]	4.7 uF [TAJT475K016RNJ]	4.7 uF [TPSB475K025R070 0]
4.7 uF [TACL475K010RTA]	4.7 uF [TAJD475K035RNJ]	4.7 uF [TAJT475K020RNJ]	4.7 uF [TPSB475K025R090 0]
4.7 uF [TAJA475K006RNJ]	4.7 uF [TAJD475K050RNJ]	4.7 uF [TAJW475K035RNJ]	4.7 uF [TPSB475K025R150 0]
4.7 uF [TAJA475K010RNJ]	4.7 uF [TAJK475K016RNJ]	4.7 uF [THJA475K006RJN]	4.7 uF [TPSB475K025R150 0]
4.7 uF [TAJA475K016RNJ]	4.7 uF [TAJP475K016RNJ]	4.7 uF [THJA475K016RJN]	4.7 uF [TPSB475K035R150 0]
4.7 uF [TAJA475K020RNJ]	4.7 uF [TAJR475K002RNJ]	4.7 uF [THJB475K016RJN]	4.7 uF [TPSC475K025R070 0]
4.7 uF [TAJA475K025RNJ]	4.7 uF [TAJR475K004RNJ]	4.7 uF [THJC475K035RJN]	4.7 uF [TPSC475K035R060 0]
4.7 uF [TAJB475K010RNJ]	4.7 uF [TAJR475K006RNJ]	4.7 uF [THJD475K050RJN]	4.7 uF [TPSC475K050R080 0]
4.7 uF [TAJB475K016RNJ]	4.7 uF [TAJR475K010RNJ]	4.7 uF [TPSA475K010R140 0]	4.7 uF [TPSC475K050R080 0]
4.7 uF [TAJB475K020RNJ]	4.7 uF [TAJS475K004RNJ]	4.7 uF [TPSA475K016R200 0]	

Multisim 14.1 Education Components

4.7 uF [TPSD475K035R070 0]	4.7 uH [SDE0604A- 4R7M]	4.7 uH [SDR6603- 4R7M]	4.7 uH [SRP1235- 4R7M]
4.7 uF [TPSD475K050R030 0]	4.7 uH [SDE0805A- 4R7M]	4.7 uH [SDR7030- 4R7M]	4.7 uH [SRP1245A- 4R7M]
4.7 uF [TPSD475K050R050 0]	4.7 uH [SDE1006A- 4R7M]	4.7 uH [SDR7045- 4R7M]	4.7 uH [SRP1250- 4R7M]
4.7 uF [TPSD475K050R050 0]	4.7 uH [SDR0302- 4R7ML]	4.7 uH [SRN3010- 4R7M]	4.7 uH [SRP1265A- 4R7M]
4.7 uF [TPSD475K050R070 0]	4.7 uH [SDR0403- 4R7ML]	4.7 uH [SRN3015- 4R7M]	4.7 uH [SRP1270- 4R7M]
4.7 uF [TPSR475K010R300 0]	4.7 uH [SDR0603- 4R7ML]	4.7 uH [SRN4012T- 4R7M]	4.7 uH [SRP1770TA-4R7M]
4.7 uF [TPSR475K010R500 0]	4.7 uH [SDR0604- 4R7ML]	4.7 uH [SRN4018- 4R7M]	4.7 uH [SRP4012TA-4R7M]
4.7 uF [TPSR475K010R500 0]	4.7 uH [SDR0703- 4R7ML]	4.7 uH [SRN4026- 4R7M]	4.7 uH [SRP4020- 4R7M]
4.7 uF [TPSS475K006R400 0]	4.7 uH [SDR0805- 4R7ML]	4.7 uH [SRN5020- 4R7M]	4.7 uH [SRP4020TA-4R7M]
4.7 uF [TRJA475K020RRJ]	4.7 uH [SDR0906- 4R7ML]	4.7 uH [SRN5040- 4R7M]	4.7 uH [SRP5015TA-4R7M]
4.7 uF [TRJB475K016RRJ]	4.7 uH [SDR1005- 4R7ML]	4.7 uH [SRN6028- 4R7M]	4.7 uH [SRP5030T- 4R7M]
4.7 uF [TRJB475K035RRJ]	4.7 uH [SDR1006- 4R7ML]	4.7 uH [SRN6045- 4R7Y]	4.7 uH [SRP5030TA-4R7M]
4.7 uF [TRJC475K035RRJ]	4.7 uH [SDR1030- 4R7M]	4.7 uH [SRN8040- 4R7Y]	4.7 uH [SRP6540- 4R7M]
4.7 uF [TRJD475K050RRJ]	4.7 uH [SDR1307- 4R7ML]	4.7 uH [SRP1038A- 4R7M]	4.7 uH [SRP7028A- 4R7M]
4.7 uH [SDE0403A- 4R7M]	4.7 uH [SDR1307A- 4R7M]	4.7 uH [SRP1040- 4R7M]	4.7 uH [SRP7030- 4R7FM]

Multisim 14.1 Education Components

4.7 uH [SRP7050TA-4R7M]	4.7 uH [SRR4018- 4R7Y]	4.7 uH [SRU3017- 4R7Y]	4.75 kOhm [CR0402-FX- 4751GLF]
4.7 uH [SRR0603- 4R7ML]	4.7 uH [SRR4028- 4R7Y]	4.7 uH [SRU5011- 4R7Y]	4.75 kOhm [CR0603-FX- 4751ELF]
4.7 uH [SRR0604- 4R7ML]	4.7 uH [SRR6603- 4R7ML]	4.7 uH [SRU5016- 4R7Y]	4.75 kOhm [CR0603-FX- 4751GLF]
4.7 uH [SRR0618- 4R7ML]	4.7 uH [SRR7032- 4R7M]	4.7 uH [SRU5018- 4R7Y]	4.75 kOhm [CR0805-FX- 4751ELF]
4.7 uH [SRR0906- 4R7ML]	4.7 uH [SRR7045- 4R7M]	4.7 uH [SRU5028- 4R7Y]	4.75 kOhm [CR1206-FX- 4751ELF]
4.7 uH [SRR1003- 4R7M]	4.7 uH [SRU1028- 4R7Y]	4.7 uH [SRU5028A- 4R7Y]	4.75 kOhm [CRM0805-FX- 4751ELF]
4.7 uH [SRR1005- 4R7M]	4.7 uH [SRU1028A- 4R7Y]	4.7 uH [SRU6011- 4R7Y]	4.75 kOhm [CRM1206-FX- 4751ELF]
4.7 uH [SRR1210- 4R7Y]	4.7 uH [SRU1048- 4R7Y]	4.7 uH [SRU6018- 4R7Y]	4.75 kOhm [CRM2512-FX- 4751ELF]
4.7 uH [SRR1210A- 4R7Y]	4.7 uH [SRU1048A- 4R7Y]	4.7 uH [SRU6025- 4R7Y]	4.75 kOhm [CRT0402-BY- 4751GLF]
4.7 uH [SRR1240- 4R7M]	4.7 uH [SRU1063- 4R7Y]	4.7 uH [SRU6025A- 4R7Y]	4.75 kOhm [CRT0603-BW- 4751ELF]
4.7 uH [SRR1260- 4R7Y]	4.7 uH [SRU2011- 4R7Y]	4.7 uH [SRU8028- 4R7Y]	4.75 kOhm [CAY16- 4751F4LF]
4.7 uH [SRR1260A- 4R7Y]	4.7 uH [SRU2013- 4R7Y]	4.7 uH [SRU8028A- 4R7Y]	4.75 kOhm [CAY16- 4751F4LF]
4.7 uH [SRR1280- 4R7Y]	4.7 uH [SRU2016- 4R7Y]	4.7 uH [SRU8043- 4R7Y]	4.75 kOhm [CAY16- 4751F4LF]
4.7 uH [SRR3011- 4R7YL]	4.7 uH [SRU3011- 4R7Y]	4.75 kOhm [CAT16- 4751F4LF]	4.75 kOhm [CAY16- 4751F4LF]
4.7 uH [SRR4011- 4R7YL]	4.7 uH [SRU3014- 4R7Y]	4.75 kOhm [CAY16- 4751F4LF]	4.75 kOhm [CAY16- 4751F4LF]

Multisim 14.1 Education Components

4.75 kOhm [CRT0603-DZ- 4751ELF]	4.87 kOhm [CRT1206-FZ- 4871ELF]	4.99 kOhm [CRT0603-BY- 4991ELF]	40 kOhm [PWR221T-30- 4002F]
4.75 kOhm [CRT1206-DW- 4751ELF]	4.99 kOhm [CAT16- 4991F4LF]	4.99 kOhm [CRT0603-FY- 4991EAS]	40 mOhm [CRA2512-FZ- R040ELF]
4.75 Ohm [CRL0805-FW- 4R75ELF]	4.99 kOhm [CAY16- 4991F4LF]	4.99 kOhm [CRT0603-FY- 4991ELF]	40 mOhm [CRA2512-JZ- R040ELF]
4.75 Ohm [CRM1206-FX- 4R75ELF]	4.99 kOhm [CR0201-FW- 4991GLF]	4.99 kOhm [CRT0805-BY- 4991ELF]	40 mOhm [CRF2512-FZ- R040ELF]
4.8 kOhm [4116R- 1-482]	4.99 kOhm [CR0402-FX- 4991GLF]	4.99 kOhm [CRT0805-DY- 4991ELF]	40 mOhm [CRL1206-FV- R040ELF]
4.8 kOhm [4116R- 1-482LF]	4.99 kOhm [CR0603-FX- 4991ELF]	4.99 MOhm [CHV0805-FX- 4994ELF]	40 mOhm [PWR163S-25- R040JE]
4.87 kOhm [CR0201-FW- 4871GLF]	4.99 kOhm [CR0805-FX- 4991ELF]	4.99 MOhm [CR0603-FX- 4994ELF]	40 mOhm [PWR221T-30- R040J]
4.87 kOhm [CR0402-FX- 4871GLF]	4.99 kOhm [CR1206-FX- 4991ELF]	4.99 Ohm [CRL1206-FW- 4R99ELF]	40 mOhm [PWR4412- 2SBR0400F]
4.87 kOhm [CR0603-FX- 4871ELF]	4.99 kOhm [CRM1206-FX- 4991ELF]	4.99 Ohm [CRM1206-FX- 4R99ELF]	40 mOhm [PWR4412- 2SCR0400F]
4.87 kOhm [CR0805-FX- 4871ELF]	4.99 kOhm [CRM2512-FX- 4991ELF]	4.99 Ohm [CRS2010-FW- 4R99ELF]	40 Ohm [PWR163S-25- 40R0F]
4.87 kOhm [CR1206-FX- 4871ELF]	4.99 kOhm [CRT0402-BY- 4991GLF]	4.99 Ohm [CRT0603-BY- 4R99ELF]	40 Ohm [PWR163S-25- 40R0FE]
4.87 kOhm [CRT0603-BY- 4871ELF]	4.99 kOhm [CRT0603-BV- 4991ELF]	4_AMP	

Multisim 14.1 Education Components

40 Ohm [PWR163S-25-40R0J]	40.2 kOhm [CRM2512-FX-4022ELF]	40.2 Ohm [CRT0402-BY-40R2GLF]	400 Ohm [PWR220T-35-4000J]
40 Ohm [PWR220T-20-40R0F]	40.2 kOhm [CRT0603-BY-4022ELF]	40.2 Ohm [CRT0402-FZ-40R2GLF]	4000BD_10V
40 Ohm [PWR221T-30-40R0F]	40.2 kOhm [CRT0603-DW-4022ELF]	40.2 Ohm [CRT0805-BY-40R2ELF]	4000BD_15V
40 Ohm [PWR263S-20-40R0J]	40.2 kOhm [CRT0805-BY-4022ELF]	40.2 Ohm [CRT1206-BY-40R2ELF]	4000BD_5V
40 Ohm [PWR263S-35-40R0F]	40.2 kOhm [CRT1206-BY-4022ELF]	40 AMP	4000BP_10V
40 Ohm [PWR263S-35-40R0J]	40.2 kOhm [CRT1206-FZ-4022ELF]	400 mOhm [PWR163S-25-R400FE]	4000BP_15V
40.2 kOhm [CAT16-4022F4LF]	40.2 Ohm [CAT16-40R2F4LF]	400 mOhm [PWR220T-35-R400F]	4000BP_5V
40.2 kOhm [CR0402-FX-4022GLF]	40.2 Ohm [CAY16-40R2F4LF]	400 mOhm [PWR221T-30-R400F]	4000BT_10V
40.2 kOhm [CR0603-FX-4022ELF]	40.2 Ohm [CR0201-FW-40R2GLF]	400 mOhm [PWR263S-35-R400F]	4000BT_15V
40.2 kOhm [CR0805-FX-4022ELF]	40.2 Ohm [CR0402-FX-40R2GLF]	400 nH [SRP7050TA-R40M]	4001BD_10V
40.2 kOhm [CR1206-FX-4022ELF]	40.2 Ohm [CR0603-FX-40R2ELF]	400 Ohm [4814P-T02-401]	4001BD_15V
	40.2 Ohm [CR0805-FX-40R2ELF]	400 Ohm [PWR163S-25-4000F]	4001BD_5V
	40.2 Ohm [CR1206-FX-40R2ELF]		4001BP_10V
			4001BP_15V
			4001BP_5V
			4001BP_5V
			4001BT_10V
			4001BT_15V
			4001BT_5V
			4002BD_10V
			4002BD_15V
			4002BD_5V

Multisim 14.1 Education Components

4002BP_10V	4009BD_15V	4011BD_10V	4013BP_5V
4002BP_15V	4009BD_5V	4011BD_15V	4013BP_5V
4002BP_5V	40106BD_10V	4011BD_5V	4013BT_10V
4002BP_5V	40106BD_15V	4011BP_10V	4013BT_15V
4002BT_10V	40106BD_5V	4011BP_15V	4013BT_5V
4002BT_15V	40106BP_10V	4011BP_5V	4014BD_10V
4002BT_5V	40106BP_15V	4011BP_5V	4014BD_15V
4008BD_10V	40106BP_5V	4011BT_10V	4014BD_5V
4008BD_15V	40106BP_5V	4011BT_15V	4014BP_10V
4008BD_5V	40106BT_10V	4011BT_5V	4014BP_15V
4008BP_10V	40106BT_15V	4012BD_10V	4014BP_5V
4008BP_15V	40106BT_5V	4012BD_15V	4014BP_5V
4008BP_5V	4010BC1_10V	4012BD_5V	4014BT_10V
4008BP_5V	4010BC1_15V	4012BP_10V	4014BT_15V
4008BT_10V	4010BC1_5V	4012BP_15V	4014BT_5V
4008BT_15V	4010BEY_10V	4012BP_5V	4015BD_10V
4008BT_5V	4010BEY_15V	4012BP_5V	4015BD_15V
4009BCL_10V	4010BEY_5V	4012BT_10V	4015BD_5V
4009BCL_15V	4010BF_10V	4012BT_15V	4015BP_10V
4009BCL_5V	4010BF_15V	4012BT_5V	4015BP_15V
4009BCP_10V	4010BF_5V	4013BD_10V	4015BP_5V
4009BCP_15V	4010BF_5V	4013BD_15V	4015BP_5V
4009BCP_5V	4010BM1_10V	4013BD_5V	4015BT_10V
4009BCP_5V	4010BM1_15V	4013BP_10V	4015BT_15V
4009BD_10V	4010BM1_5V	4013BP_15V	4015BT_5V

Multisim 14.1 Education Components

40160BD_10V	40162BT_15V	40175BP_5V	40192BD_15V
40160BD_15V	40162BT_5V	40175BT_10V	40192BD_5V
40160BD_5V	40163BD_10V	40175BT_15V	40192BP_10V
40160BP_10V	40163BD_15V	40175BT_5V	40192BP_15V
40160BP_15V	40163BD_5V	4017BD_10V	40192BP_5V
40160BP_5V	40163BP_10V	4017BD_15V	40192BT_10V
40160BT_10V	40163BP_15V	4017BD_5V	40192BT_15V
40160BT_15V	40163BP_5V	4017BP_10V	40192BT_5V
40160BT_5V	40163BT_10V	4017BP_10V	40193BD_10V
40161BD_10V	40163BT_15V	4017BP_15V	40193BD_15V
40161BD_15V	40163BT_5V	4017BP_5V	40193BD_5V
40161BD_5V	40174BD_10V	4017BP_5V	40193BP_10V
40161BP_10V	40174BD_15V	4017BT_10V	40193BP_15V
40161BP_15V	40174BD_5V	4017BT_15V	40193BP_5V
40161BP_5V	40174BP_10V	4017BT_5V	40193BT_10V
40161BT_10V	40174BP_15V	4018BD_10V	40193BT_15V
40161BT_15V	40174BP_5V	4018BD_15V	40193BT_5V
40161BT_5V	40174BT_10V	4018BD_5V	40194BD_10V
40162BD_10V	40174BT_15V	4018BP_10V	40194BD_15V
40162BD_15V	40174BT_5V	4018BP_15V	40194BD_5V
40162BD_5V	40175BD_10V	4018BP_5V	40194BP_10V
40162BP_10V	40175BD_15V	4018BT_10V	40194BP_15V
40162BP_15V	40175BD_5V	4018BT_15V	40194BP_5V
40162BP_5V	40175BP_10V	4018BT_5V	40194BT_10V
40162BT_10V	40175BP_15V	40192BD_10V	40194BT_15V

Multisim 14.1 Education Components

40194BT_5V	402 kOhm	402 Ohm	4023BD_15V
40195BD_10V	[CR0805-FX-4023ELF]	[CRT0805-BY-4020ELF]	4023BD_5V
40195BD_15V	402 kOhm	402 Ohm	4023BP_10V
40195BD_5V	[CR1206-FX-4023ELF]	[PWR4318W4020FE]	4023BP_15V
40195BP_10V	402 kOhm	4020BD_10V	4023BP_5V
40195BP_15V	[CR2512-FX-4023ELF]	4020BD_15V	4023BP_5V
40195BP_5V	402 kOhm	4020BD_5V	4023BT_10V
40195BT_10V	[CRT0805-BY-4023ELF]	4020BP_10V	4023BT_15V
40195BT_15V	402 kOhm	4020BP_10V	4023BT_5V
40195BT_5V	[CRT1206-BY-4023ELF]	4020BP_15V	40240BP_10V
4019BD_10V	402 kOhm	4020BP_5V	40240BP_15V
4019BD_15V	402 kOhm	4020BT_10V	40240BP_5V
4019BD_5V	[CRT1206-FZ-4023ELF]	4020BT_15V	40240BT_10V
4019BP_10V	402 Ohm [CR0402-FX-4020GLF]	4020BT_5V	40240BT_15V
4019BP_15V	402 Ohm [CR0603-FX-4020ELF]	4021BD_10V	40240BT_5V
4019BP_5V	402 Ohm [CR0805-FX-4020ELF]	4021BD_15V	40244BP_10V
4019BT_10V	402 Ohm [CR1206-FX-4020ELF]	4021BD_5V	40244BP_15V
4019BT_15V	402 Ohm [CR1206-FX-4020ELF]	4021BP_10V	40244BP_5V
4019BT_5V	402 Ohm	4021BP_15V	40244BT_10V
402 kOhm	[CRT0402-FZ-4020GLF]	4021BP_5V	40244BT_15V
[CR0402-FX-4023GLF]	402 Ohm	4021BT_10V	40244BT_5V
402 kOhm	[CRT0603-BV-4020ELF]	4021BT_15V	40245BP_10V
[CR0603-FX-4023ELF]	402 Ohm	4021BT_5V	40245BP_15V
		4023BD_10V	40245BP_5V
			40245BT_10V

Multisim 14.1 Education Components

40245BT_15V	4027BP_10V	4029BT_5V	4035BP_5V
40245BT_5V	4027BP_15V	4030BD_10V	4035BT_10V
4024BD_10V	4027BP_5V	4030BD_15V	4035BT_15V
4024BD_15V	4027BP_5V	4030BD_5V	4035BT_5V
4024BD_5V	4027BT_10V	4030BP_10V	40373BP_10V
4024BP_10V	4027BT_15V	4030BP_15V	40373BP_15V
4024BP_15V	4027BT_5V	4030BP_5V	40373BP_5V
4024BP_5V	4028BD_10V	4030BP_5V	40373BT_10V
4024BP_5V	4028BD_15V	4030BT_10V	40373BT_15V
4024BT_10V	4028BD_5V	4030BT_15V	40373BT_5V
4024BT_15V	4028BP_10V	4030BT_5V	40374BP_10V
4024BT_5V	4028BP_15V	4032BCL_10V	40374BP_15V
4025BD_10V	4028BP_5V	4032BCL_15V	40374BP_5V
4025BD_15V	4028BP_5V	4032BCL_5V	40374BT_10V
4025BD_5V	4028BT_10V	4032BCP_10V	40374BT_15V
4025BP_10V	4028BT_15V	4032BCP_15V	40374BT_5V
4025BP_15V	4028BT_5V	4032BCP_5V	4038BCL_10V
4025BP_5V	4029BD_10V	4032BD_10V	4038BCL_15V
4025BP_5V	4029BD_15V	4032BD_15V	4038BCL_5V
4025BT_10V	4029BD_5V	4032BD_5V	4038BCP_10V
4025BT_15V	4029BP_10V	4035BD_10V	4038BCP_15V
4025BT_5V	4029BP_15V	4035BD_15V	4038BCP_5V
4027BD_10V	4029BP_5V	4035BD_5V	4038BD_10V
4027BD_15V	4029BT_10V	4035BP_10V	4038BD_15V
4027BD_5V	4029BT_15V	4035BP_15V	4038BD_5V

Multisim 14.1 Education Components

4040BD_10V	4042BP_5V	4049BD_10V	4060BP_5V
4040BD_15V	4042BP_5V	4049BD_15V	4060BT_10V
4040BD_5V	4042BT_10V	4049BD_5V	4060BT_15V
4040BP_10V	4042BT_15V	4049BP_10V	4060BT_5V
4040BP_15V	4042BT_5V	4049BP_15V	4066BD_10V
4040BP_5V	4043BD_10V	4049BP_5V	4066BD_15V
4040BP_5V	4043BD_15V	4049BP_5V	4066BD_5V
4040BT_10V	4043BD_5V	4049BT_10V	4066BP_10V
4040BT_15V	4043BP_10V	4049BT_15V	4066BP_15V
4040BT_5V	4043BP_15V	4049BT_5V	4066BP_5V
4041BD_10V	4043BP_5V	4050BD_10V	4066BT_10V
4041BD_15V	4043BP_5V	4050BD_15V	4066BT_15V
4041BD_5V	4043BT_10V	4050BD_5V	4066BT_5V
4041BP_10V	4043BT_15V	4050BP_10V	4068BD_10V
4041BP_15V	4043BT_5V	4050BP_15V	4068BD_15V
4041BP_5V	4044BD_10V	4050BP_5V	4068BD_5V
4041BP_5V	4044BD_15V	4050BP_5V	4068BP_10V
4041BT_10V	4044BD_5V	4050BT_10V	4068BP_15V
4041BT_15V	4044BP_10V	4050BT_15V	4068BP_5V
4041BT_5V	4044BP_15V	4050BT_5V	4068BP_5V
4042BD_10V	4044BP_5V	4060BD_10V	4068BT_10V
4042BD_15V	4044BP_5V	4060BD_15V	4068BT_15V
4042BD_5V	4044BT_10V	4060BD_5V	4068BT_5V
4042BP_10V	4044BT_15V	4060BP_10V	4069BCL_10V
4042BP_15V	4044BT_5V	4060BP_15V	4069BCL_15V

Multisim 14.1 Education Components

4069BCL_5V	4071BT_10V	4075BD_5V	4077BT_10V
4069BCP_10V	4071BT_15V	4075BP_10V	4077BT_15V
4069BCP_15V	4071BT_5V	4075BP_15V	4077BT_5V
4069BCP_5V	4072BD_10V	4075BP_5V	4078BD_10V
4069BCP_5V	4072BD_15V	4075BP_5V	4078BD_15V
4069BD_10V	4072BD_5V	4075BT_10V	4078BD_5V
4069BD_15V	4072BP_10V	4075BT_15V	4078BP_10V
4069BD_5V	4072BP_15V	4075BT_5V	4078BP_15V
4070BD_10V	4072BP_5V	4076BD_10V	4078BP_5V
4070BD_15V	4072BP_5V	4076BD_15V	4078BP_5V
4070BD_5V	4072BT_10V	4076BD_5V	4078BT_10V
4070BP_10V	4072BT_15V	4076BD_5V	4078BT_15V
4070BP_15V	4072BT_5V	4076BP_10V	4078BT_5V
4070BP_5V	4073BD_10V	4076BP_15V	4081BD_10V
4070BP_5V	4073BD_15V	4076BP_5V	4081BD_15V
4070BT_10V	4073BD_5V	4076BT_10V	4081BD_5V
4070BT_15V	4073BP_10V	4076BT_15V	4081BP_10V
4070BT_5V	4073BP_15V	4076BT_5V	4081BP_15V
4071BD_10V	4073BP_5V	4077BD_10V	4081BP_5V
4071BD_15V	4073BP_5V	4077BD_15V	4081BP_5V
4071BD_5V	4073BT_10V	4077BD_5V	4081BT_10V
4071BP_10V	4073BT_15V	4077BP_10V	4081BT_15V
4071BP_15V	4073BT_5V	4077BP_15V	4081BT_5V
4071BP_5V	4075BD_10V	4077BP_5V	4082BD_10V
4071BP_5V	4075BD_15V	4077BP_5V	4082BD_15V

Multisim 14.1 Education Components

4082BD_5V	4086BT_10V	4099BCP_10V	41.2 Ohm [CR0603-FX-41R2ELF]
4082BP_10V	4086BT_15V	4099BCP_15V	
4082BP_15V	4086BT_5V	4099BCP_5V	41.2 Ohm [CR0805-FX-41R2ELF]
4082BP_5V	4093BD_10V	4099BDW_10V	41.2 Ohm [CR1206-FX-41R2ELF]
4082BP_5V	4093BD_15V	4099BDW_15V	
4082BT_10V	4093BD_5V	4099BDW_5V	4108R-3-121/121LF
4082BT_15V	4093BP_10V	40EPS08	4108R-3-221/221LF
4082BT_5V	4093BP_15V	40EPS12	4108R-3-221/331LF
4085BD_10V	4093BP_5V	40EPS16	4114R-3-104/103
4085BD_15V	4093BP_5V	41 kOhm [4608X-102-413LF]	4114R-3-121/201
4085BD_5V	4093BT_10V		4114R-3-152/332
4085BP_10V	4093BT_15V	41 kOhm [4609X-101-413LF]	4114R-3-161/261
4085BP_15V	4093BT_5V	41 kOhm [4610H-101-413LF]	4114R-3-181/391
4085BP_5V	4094BD_10V		4114R-3-181/391LF
4085BP_5V	4094BD_15V	41.2 kOhm [CR0402-FX-4122GLF]	4114R-3-221/271
4085BT_10V	4094BD_5V		4114R-3-221/331
4085BT_15V	4094BP_10V	41.2 kOhm [CR0603-FX-4122ELF]	4114R-3-221/331LF
4085BT_5V	4094BP_15V		4114R-3-302/622
4086BD_10V	4094BP_5V	41.2 kOhm [CR0805-FX-4122ELF]	4114R-3-302/622LF
4086BD_15V	4094BT_10V		4114R-3-331/391
4086BD_5V	4094BT_15V	41.2 kOhm [CR1206-FX-4122ELF]	4114R-3-331/391LF
4086BD_5V	4094BT_5V		4114R-3-331/471
4086BP_10V	4099BCL_10V		4114R-3-331/471LF
4086BP_15V	4099BCL_15V	41.2 kOhm [CRT1206-BY-4122ELF]	4114R-3-331/681
4086BP_5V	4099BCL_5V		4114R-3-331/681LF

Multisim 14.1 Education Components

4114R-3-361/781	4116R-3-331/471LF	412 Ohm [CR0402-FX-4120GLF]	42.2 Ohm [CR0805-FX-42R2ELF]
4114R-3-391/821	4116R-3-331/681		
4114R-3-750/621	4116R-3-331/681LF	412 Ohm [CR0603-FX-4120ELF]	42.2 Ohm [CR0805-FX-42R2GLF]
4116R-3-121/201	4116R-3-361/781	412 Ohm [CR0805-FX-4120ELF]	42.2 Ohm [CR1206-FX-42R2ELF]
4116R-3-152/332	4116R-3-361/781LF		
4116R-3-152/332LF	4116R-3-391/821	412 Ohm [CR1206-FX-4120ELF]	422 kOhm [CR0402-FX-4223GLF]
4116R-3-161/241	4116R-3-391/821LF	412 Ohm [CRT1206-BY-4120ELF]	422 kOhm [CR0603-FX-4223ELF]
4116R-3-161/241LF	4116R-3-431/821		
4116R-3-161/261	4116R-3-471/681	413990-1	
4116R-3-161/261LF	4116R-3-471/681LF	42.2 kOhm [CR0402-FX-4222GLF]	422 kOhm [CR0805-FX-4223ELF]
4116R-3-181/391	4116R-3-621/911		
4116R-3-181/391LF	4116R-3-621/911LF	42.2 kOhm [CR0603-FX-4222ELF]	422 kOhm [CR1206-FX-4223ELF]
4116R-3-220/330	4116R-3-681/102		
4116R-3-221/271	4116R-3-681/681	42.2 kOhm [CR0805-FX-4222ELF]	422 Ohm [CR0402-FX-4220GLF]
4116R-3-221/271LF	4116R-3-681/681LF		
4116R-3-221/331	4116R-3-820/131	42.2 kOhm [CR1206-FX-4222ELF]	422 Ohm [CR0603-FX-4220ELF]
4116R-3-221/331LF	412 kOhm [CR0603-FX-4123ELF]		
4116R-3-221/391		42.2 kOhm [CR1206-FX-4222ELF]	422 Ohm [CR0805-FX-4220ELF]
4116R-3-221/391LF	412 kOhm [CR0805-FX-4123ELF]		
4116R-3-302/622		42.2 kOhm [CRT0402-FZ-4222GLF]	422 Ohm [CR1206-FX-4220ELF]
4116R-3-302/622LF	412 kOhm [CR1206-FX-4123ELF]		
4116R-3-330/390		42.2 Ohm [CR0402-FX-42R2GLF]	422 Ohm [CRT0402-FZ-4220GLF]
4116R-3-331/391			
4116R-3-331/391LF	412 kOhm [CRM2512-FX-4123ELF]	42.2 Ohm [CR0603-FX-42R2ELF]	43 kOhm [4116R-1-433]
4116R-3-331/471			

Multisim 14.1 Education Components

43 kOhm [CAT16-433J4LF]	43 Ohm [4116R-2-430LF]	43 Ohm [CR0603-JW-430ELF]	43 pF [C2225C430KBGAC TU]
43 kOhm [CAY16-433J4LF]	43 Ohm [4308R-102-430LF]	43 Ohm [CR0805-FX-43R0ELF]	43.2 kOhm [CR0402-FX-4322GLF]
43 kOhm [CAY17-433JALF]	43 Ohm [4310R-102-430]	43 Ohm [CR0805-FX-43R0GLF]	43.2 kOhm [CR0603-FX-4322ELF]
43 kOhm [CR0201-FW-4302GLF]	43 Ohm [4420P-1-430]	43 Ohm [CR0805-JW-430ELF]	43.2 kOhm [CR0805-FX-4322ELF]
43 kOhm [CR0402-FX-4302GLF]	43 Ohm [4816P-1-430]	43 Ohm [CR1206-FX-43R0ELF]	43.2 kOhm [CR1206-FX-4322ELF]
43 kOhm [CR0603-FX-4302ELF]	43 Ohm [4816P-1-430LF]	43 Ohm [CR1206-JW-430ELF]	43.2 kOhm [CR1206-FX-4322ELF]
43 kOhm [CR0603-JW-433ELF]	43 Ohm [CAT10-430J4LF]	43 Ohm [CRM2512-FX-43R0ELF]	43.2 Ohm [CR0402-FX-43R2GLF]
43 kOhm [CR0805-FX-4302ELF]	43 Ohm [CAT16-430J4LF]	43 pF [C0805C430KBGAC TU]	43.2 Ohm [CR0603-FX-43R2ELF]
43 kOhm [CR0805-JW-433ELF]	43 Ohm [CAT25-430JALF]	43 pF [C1206C430KBGAC TU]	43.2 Ohm [CR0603-FX-43R2GLF]
43 kOhm [CR1206-FX-4302ELF]	43 Ohm [CAY10-430J4LF]	43 pF [C1210C430KBGAC TU]	43.2 Ohm [CR0805-FX-43R2ELF]
43 kOhm [CR1206-JW-433ELF]	43 Ohm [CAY16-430J4LF]	43 pF [C1812C430KBGAC TU]	43.2 Ohm [CR1206-FX-43R2ELF]
43 kOhm [CRM2512-JW-433ELF]	43 Ohm [CAY16-43R0F4LF]	43 pF [C1825C430KBGAC TU]	43.2 Ohm [CRM2512-FX-43R2ELF]
43 mF [C0805C439KBGAC TU]	43 Ohm [CR0402-FX-43R0GLF]	43 pF [C2220C430KBGAC TU]	430 kOhm [CAY16-434J4LF]
43 Ohm [4116R-1-430]	43 Ohm [CR0603-FX-43R0ELF]		
43 Ohm [4116R-2-430]			

Multisim 14.1 Education Components

430 kOhm [CR0402-FX-4303GLF]	430 mOhm [CRL1206-FW-R430ELF]	430 Ohm [4816P-2-431]	430 Ohm [CR0805-JW-431ELF]
430 kOhm [CR0603-FX-4303ELF]	430 mOhm [CRL1206-JW-R430ELF]	430 Ohm [4816P-2-431LF]	430 Ohm [CR1206-FX-4300ELF]
430 kOhm [CR0603-JW-434ELF]	430 mOhm [CRL2010-FW-R430ELF]	430 Ohm [4816P-T01-431]	430 Ohm [CR1206-JW-431ELF]
430 kOhm [CR0805-FX-4303ELF]	430 mOhm [CRL2010-JW-R430ELF]	430 Ohm [4816P-T02-431]	430 Ohm [CR2512-JW-431ELF]
430 kOhm [CR0805-JW-434ELF]	430 mOhm [CRL2512-FW-R430ELF]	430 Ohm [4816P-T02-431LF]	430 pF [C0402C431K1HACTU]
430 kOhm [CR1206-FX-4303ELF]	430 mOhm [CRL2512-JW-R430ELF]	430 Ohm [CAT16-431J4LF]	430 pF [C0402C431K3HACTU]
430 kOhm [CR1206-JW-434ELF]	430 mOhm [CRM2512-FX-R430ELF]	430 Ohm [CAT25-431JALF]	430 pF [C0402C431K5HACTU]
430 mOhm [CRL0603-FW-R430ELF]	430 Ohm [4116R-1-431]	430 Ohm [CAY16-431J4LF]	430 pF [C0603C431K1HACTU]
430 mOhm [CRL0603-JW-R430ELF]	430 Ohm [4308R-102-431]	430 Ohm [CR0201-FW-4300GLF]	430 pF [C0603C431K3HACTU]
430 mOhm [CRL0805-FW-R430ELF]	430 Ohm [4310R-102-431]	430 Ohm [CR0402-FX-4300GLF]	430 pF [C0603C431K5HACTU]
430 mOhm [CRL0805-JW-R430ELF]	430 Ohm [4608X-102-431LF]	430 Ohm [CR0402-JW-431GLF]	430 pF [C1206C431KBGAC TU]
	430 Ohm [4816P-1-431]	430 Ohm [CR0603-FX-4300ELF]	
	430 Ohm [4816P-1-431LF]	430 Ohm [CR0603-JW-431ELF]	
		430 Ohm [CR0805-FX-4300ELF]	

Multisim 14.1 Education Components

430 pF [C1210C431KBGAC TU]	4306R-104- 161/241L	4308H-104- 221/331L	4308R-104-221/271
	4306R-104-180/390		4308R-104-221/331
430 pF [C1812C431KBGAC TU]	4306R-104-181/391	4308M-104- 221/331	4308R-104- 221/331L
430 pF [C1825C431KBGAC TU]	4306R-104- 181/391L	4308M-104- 221/331L	4308R-104-271/271
	4306R-104- 221/271L	4308M-104- 331/471	4308R-104-302/622
430 pF [C2220C431KBGAC TU]	4306R-104-221/331	4308M-104- 331/471L	4308R-104-302/622L
	4306R-104- 221/331L	4308R-104-102/202	4308R-104- 331/331L
430 pF [C2225C431KBGAC TU]	4306R-104-302/622	4308R-104-103/203	4308R-104-331/391
	4306R-104- 302/622L	4308R-104- 103/203L	4308R-104-331/391L
4304M-104- 121/191	4306R-104-331/391	4308R-104-112/112	4308R-104-331/471
	4306R-104- 331/391L	4308R-104- 112/112L	4308R-104- 331/471L
4304M-104- 121/481	4306R-104-331/471	4308R-104-121/131	4308R-104-331/681
	4306R-104- 331/471L	4308R-104-152/332	4308R-104- 331/681L
4304M-104- 161/111	4306R-104-810/131	4308R-104- 161/241L	4308R-104-332/472
	4306R-104- 810/131L	4308R-104-161/261	4308R-104-681/102
4304M-104- 221/331	4308H-104- 181/391	4308R-104-181/241	4308R-104-810/131
	4308H-104- 181/391L	4308R-104- 181/241L	4308R-104- 810/131L
4306R-104-121/191		4308R-104-181/391	4308R-104-820/131
4306R-104-121/201	4308H-104- 221/331	4308R-104- 181/391L	4308R-104- 820/131L
4306R-104-161/241			

Multisim 14.1 Education Components

4310H-104- 161/241	4310M-104- 181/391	4310R-104-121/191	4310R-104-271/271
4310H-104- 161/241L	4310M-104- 181/391L	4310R-104-152/332	4310R-104- 271/271L
4310H-104- 181/391	4310M-104- 221/151	4310R-104- 152/332L	4310R-104-272/472
4310H-104- 181/391L	4310M-104- 221/151L	4310R-104-161/241	4310R-104-302/622
4310H-104- 221/271	4310M-104- 221/331	4310R-104- 161/241L	4310R-104- 302/622L
4310H-104- 221/271L	4310M-104- 221/331L	4310R-104-161/261	4310R-104-330/470
4310H-104- 221/331	4310M-104- 271/391	4310R-104- 161/261L	4310R-104-331/391
4310H-104- 221/331L	4310M-104- 302/622	4310R-104-181/221	4310R-104- 331/391L
4310H-104- 221/800	4310M-104- 302/622L	4310R-104-181/241	4310R-104-331/471
4310H-104- 221/800L	4310M-104- 331/471	4310R-104-181/331	4310R-104- 331/471L
4310H-104- 331/471	4310M-104- 331/471L	4310R-104-181/391	4310R-104-331/681
4310H-104- 331/471L	4310M-104- 820/820	4310R-104- 181/391L	4310R-104- 331/681L
4310H-104- 331/681	4310M-104- 820/820L	4310R-104-181/681	4310R-104-391/561
4310H-104- 471/102L	4310R-104-111/221	4310R-104- 181/681L	4310R-104- 391/561L
4310H-104- 820/131	4310R-104- 111/221L	4310R-104-221/181	4310R-104-391/581
	4310R-104-121/181	4310R-104- 221/182L	4310R-104-391/681
		4310R-104-221/271	4310R-104-471/681
		4310R-104-221/271L	4310R-104- 471/681L
		4310R-104-221/331	4310R-104-501/501
		4310R-104- 221/331L	4310R-104-681/102

Multisim 14.1 Education Components

4310R-104-681/102L	432 Ohm [CR1206-FX-4320ELF]	442 kOhm [CR0402-FX-4423GLF]	4420P-T03-312/182
4310R-104-810/131	432 Ohm [CR2512-FX-4320ELF]	442 kOhm [CR0603-FX-4423ELF]	4420P-T03-330/390
4310R-104-820/131	432 Ohm [CRM2512-FX-4320ELF]	442 kOhm [CR0805-FX-4423ELF]	4420P-T03-330/470
4310R-104-820/131L	432 Ohm [CRM2512-FX-4320ELF]	442 kOhm [CR0805-FX-4423ELF]	4420P-T03-331/471
4311R-104-161/241	44.2 kOhm [CR0402-FX-4422GLF]	442 kOhm [CR1206-FX-4423ELF]	45 mOhm [CRA2512-JZ-R045ELF]
4311R-104-161/241L	44.2 kOhm [CR0603-FX-4422ELF]	442 kOhm [CR1206-FX-4423ELF]	45.3 kOhm [CR0402-FX-4532GLF]
4311R-104-221/331	44.2 kOhm [CR0603-FX-4422ELF]	442 Ohm [CR0402-FX-4420GLF]	45.3 kOhm [CR0603-FX-4532ELF]
4311R-104-221/331L	44.2 kOhm [CR0805-FX-4422ELF]	442 Ohm [CR0603-FX-4420ELF]	45.3 kOhm [CR0805-FX-4532ELF]
4311R-104-331/471	44.2 kOhm [CR1206-FX-4422ELF]	442 Ohm [CR0805-FX-4420ELF]	45.3 kOhm [CR1206-FX-4532ELF]
4311R-104-331/471L	44.2 kOhm [CRM2512-FX-4422ELF]	442 Ohm [CRT0402-FZ-4420GLF]	45.3 kOhm [CRM2512-FX-4532ELF]
432 kOhm [CR0603-FX-4323ELF]	44.2 kOhm [PWR163S-25-4422JE]	4420P-3-221/331	45.3 kOhm [CRT0603-BY-4532ELF]
432 kOhm [CR0805-FX-4323ELF]	44.2 Ohm [CR0402-FX-44R2GLF]	4420P-3-302/622	45.3 Ohm [CR0201-FW-45R3GLF]
432 kOhm [CR1206-FX-4323ELF]	44.2 Ohm [CR0603-FX-44R2ELF]	4420P-3-331/391	45.3 Ohm [CR0402-FX-45R3GLF]
432 Ohm [CR0402-FX-4320GLF]	44.2 Ohm [CR0805-FX-44R2ELF]	4420P-3-331/471	45.3 Ohm [CR0603-FX-45R3ELF]
432 Ohm [CR0603-FX-4320ELF]	44.2 Ohm [CR1206-FX-44R2ELF]	4420P-T03-221/271	
432 Ohm [CR0805-FX-4320ELF]			

Multisim 14.1 Education Components

45.3 Ohm [CR0805-FX-45R3ELF]	4503BCP_5V	4511BD_15V	4514BP_5V
	4503BD_10V	4511BD_5V	4514BT_10V
45.3 Ohm [CR1206-FX-45R3ELF]	4503BD_15V	4511BP_10V	4514BT_15V
	4503BD_5V	4511BP_15V	4514BT_5V
45.3 Ohm [CR2010-FX-45R3ELF]	4508BD_10V	4511BP_5V	4515BD_10V
	4508BD_15V	4511BP_5V	4515BD_15V
45.3 Ohm [CRT0805-BY-45R3ELF]	4508BD_5V	4511BT_10V	4515BD_5V
	4508BP_10V	4511BT_15V	4515BP_10V
450 nH [SRP1038A-R45M]	4508BP_15V	4511BT_5V	4515BP_15V
4502BD_10V	4508BP_5V	4512BD_10V	4515BP_5V
4502BD_15V	4508BP_5V	4512BD_15V	4515BP_5V
4502BD_5V	4508BT_10V	4512BD_5V	4515BT_10V
4502BP_10V	4508BT_15V	4512BP_10V	4515BT_15V
4502BP_15V	4508BT_5V	4512BP_15V	4515BT_5V
4502BP_5V	4510BD_10V	4512BP_5V	4516BD_10V
4502BP_5V	4510BD_15V	4512BP_5V	4516BD_15V
4502BT_10V	4510BD_5V	4512BT_10V	4516BD_5V
4502BT_15V	4510BP_10V	4512BT_15V	4516BP_10V
4502BT_5V	4510BP_15V	4512BT_5V	4516BP_15V
4503BCL_10V	4510BP_5V	4514BD_10V	4516BP_5V
4503BCL_15V	4510BP_5V	4514BD_15V	4516BP_5V
4503BCL_5V	4510BT_10V	4514BD_5V	4516BT_10V
4503BCP_10V	4510BT_15V	4514BP_10V	4516BT_15V
4503BCP_15V	4510BT_5V	4514BP_15V	4516BT_5V
4503BCP_5V	4511BD_10V	4514BP_5V	4518BD_10V

Multisim 14.1 Education Components

4518BD_15V	4520BT_10V	453 kOhm	4531BT_10V
4518BD_5V	4520BT_15V	[CR0603-FX-4533ELF]	4531BT_15V
4518BP_10V	4520BT_5V	453 kOhm	4531BT_5V
4518BP_15V	4522BD_10V	[CR0805-FX-4533ELF]	4532BD_10V
4518BP_5V	4522BD_15V	453 kOhm	4532BD_15V
4518BP_5V	4522BD_5V	[CR1206-FX-4533ELF]	4532BD_5V
4518BT_10V	4522BP_10V		4532BP_10V
4518BT_15V	4522BP_15V	453 Ohm [CAY16-4530F4LF]	4532BP_15V
4518BT_5V	4522BP_5V	453 Ohm [CR0402-FX-4530GLF]	4532BP_5V
4519BD_10V	4522BT_10V		4532BP_5V
4519BD_15V	4522BT_15V	453 Ohm [CR0603-FX-4530ELF]	4532BT_10V
4519BD_5V	4522BT_5V		4532BT_15V
4519BP_10V	4526BD_10V	453 Ohm [CR0805-FX-4530ELF]	4532BT_5V
4519BP_15V	4526BD_15V	453 Ohm [CR1206-FX-4530ELF]	4539BD_10V
4519BP_5V	4526BD_5V		4539BD_15V
4519BT_10V	4526BP_10V	453 Ohm [CRM2512-FX-4530ELF]	4539BD_5V
4519BT_15V	4526BP_15V		4539BP_10V
4519BT_5V	4526BP_5V	453 Ohm [CRT1206-BY-4530ELF]	4539BP_15V
4520BD_10V	4526BT_10V		4539BP_5V
4520BD_15V	4526BT_15V	4531BD_10V	4539BT_10V
4520BD_5V	4526BT_5V	4531BD_15V	4539BT_15V
4520BP_10V	453 kOhm	4531BD_5V	4539BT_5V
4520BP_15V	[CR0402-FX-4533GLF]	4531BP_10V	4543BD_10V
4520BP_5V		4531BP_15V	4543BD_15V
4520BP_5V		4531BP_5V	4543BD_5V

Multisim 14.1 Education Components

4543BP_10V	4556BP_15V	46.4 kOhm	4606X-104-
4543BP_15V	4556BP_5V	[CRT0402-BY-4642GLF]	221/271L
4543BP_5V	4556BP_5V	46.4 kOhm	4606X-104-
4543BT_10V	4556BT_10V	[CRT0402-FZ-4642GLF]	221/331L
4543BT_15V	4556BT_15V	46.4 kOhm	4606X-104-
4543BT_5V	4556BT_5V	[CRT0603-PW-4642ELF]	302/622L
4544BCL_10V	4585BD_10V	46.4 kOhm	4606X-104-
4544BCL_15V	4585BD_15V	[CRT0805-BY-4642ELF]	331/471L
4544BCL_5V	4585BD_5V	46.4 Ohm [CR0402-FX-46R4GLF]	4606X-104-
4544BCP_10V	4585BP_10V	46.4 Ohm [CR0603-FX-46R4ELF]	472/472L
4544BCP_15V	4585BP_15V	46.4 Ohm [CR0805-FX-46R4ELF]	4607X-104-
4544BCP_5V	4585BP_5V	46.4 Ohm [CR1206-FX-46R4ELF]	221/331L
4555BD_10V	4585BT_10V	46.4 Ohm [CR0402-FX-46R4GLF]	4608H-104-
4555BD_15V	4585BT_15V	46.4 Ohm [CR0603-FX-46R4ELF]	101/101L
4555BD_5V	4585BT_5V	46.4 Ohm [CR0805-FX-46R4ELF]	4608H-104-
4555BP_10V	45970-4185	46.4 Ohm	500/500L
4555BP_15V	46.4 kOhm	[CRT0402-FZ-46R4GLF]	4608M-104-
4555BP_5V	[CR0402-FX-4642GLF]	4604X-104-	221/331L
4555BT_10V	46.4 kOhm	161/241L	4608X-104-
4555BT_15V	[CR0603-FX-4642ELF]	4605X-104-	161/241L
4555BT_5V	46.4 kOhm	331/391L	4608X-104-
4556BD_10V	[CR0805-FX-4642ELF]	4606X-104-	181/391L
4556BD_15V	46.4 kOhm	161/241L	4608X-104-
4556BD_5V	[CR1206-FX-4642ELF]	4606X-104-	220/330L
4556BP_10V	46.4 kOhm	181/391L	4608X-104-
			221/271L

Multisim 14.1 Education Components

4608X-104- 221/331L	4610M-104- 131/131L	4610X-104- 181/391L	4610X-104- 471/681L
4608X-104- 302/622L	4610M-104- 151/121L	4610X-104- 221/182L	4610X-104- 681/102L
4608X-104- 331/221L	4610M-104- 253/503L	4610X-104- 221/271L	4610X-104- 810/131L
4608X-104- 331/391L	4610M-104- 331/471L	4610X-104- 221/331L	4610X-104- 821/561L
4608X-104- 331/471L	4610X-104- 102/102L	4610X-104- 222/332L	4611X-104- 161/241L
4608X-104- 332/472L	4610X-104- 102/152L	4610X-104- 222/333L	4611X-104- 221/331L
4608X-104- 471/681L	4610X-104- 102/681L	4610X-104- 224/331L	4611X-104- 302/622L
4608X-104- 810/131L	4610X-104- 104/204L	4610X-104- 272/472L	4611X-104- 331/471L
4609X-104- 331/391L	4610X-104- 122/242L	4610X-104- 302/622L	4612X-104- 181/391L
4609X-104- 331/471L	4610X-104- 151/181L	4610X-104- 330/470L	4612X-104- 221/331L
4610H-104- 101/101L	4610X-104- 152/222L	4610X-104- 331/391L	4612X-104- 331/471L
4610H-104- 102/104L	4610X-104- 152/332L	4610X-104- 331/470L	4612X-104- 471/152L
4610H-104- 221/331L	4610X-104- 161/241L	4610X-104- 331/471L	4614X-104- 221/182L
4610H-104- 331/471L	4610X-104- 162/260L	4610X-104- 331/681L	4614X-104- 331/471L
4610M-104- 121/281L	4610X-104- 181/271L	4610X-104- 361/781L	464 kOhm [CR0402-FX- 4643GLF]

Multisim 14.1 Education Components

464 kOhm [CR0603-FX- 4643ELF]	47 kOhm [4108R-1- 473LF]	47 kOhm [4306R- 101-473]	47 kOhm [4309R- 101-473LF]
464 kOhm [CR0805-FX- 4643ELF]	47 kOhm [4114R-1- 473]	47 kOhm [4306R- 101-473LF]	47 kOhm [4310H- 101-473]
464 kOhm [CR1206-FX- 4643ELF]	47 kOhm [4114R-1- 473LF]	47 kOhm [4306R- 102-473]	47 kOhm [4310H- 101-473LF]
464 kOhm [CR1206-FX- 4643ELF]	47 kOhm [4114R-2- 473]	47 kOhm [4306R- 102-473LF]	47 kOhm [4310H- 102-473]
464 kOhm [CRT0603-BY- 4643ELF]	47 kOhm [4114R-2- 473LF]	47 kOhm [4308H- 101-473]	47 kOhm [4310H- 102-473LF]
464 Ohm [CAY16- 4640F4LF]	47 kOhm [4116R-1- 473]	47 kOhm [4308H- 102-473]	47 kOhm [4310M- 101-473]
464 Ohm [CR0603- FX-4640ELF]	47 kOhm [4116R-1- 473LF]	47 kOhm [4308M- 101-473]	47 kOhm [4310M- 101-473LF]
464 Ohm [CR0805- FX-4640ELF]	47 kOhm [4116R-2- 473]	47 kOhm [4308M- 101-473LF]	47 kOhm [4310M- 102-473]
464 Ohm [CR1206- FX-4640ELF]	47 kOhm [4116R-2- 473LF]	47 kOhm [4308M- 102-473]	47 kOhm [4310M- 102-473LF]
464 Ohm [CRT0402-FZ- 4640GLF]	47 kOhm [4306H- 101-473]	47 kOhm [4308M- 102-473LF]	47 kOhm [4310R- 101-473]
464 Ohm [CRT0805-BY- 4640ELF]	47 kOhm [4306H- 101-473LF]	47 kOhm [4308R- 101-473]	47 kOhm [4310R- 101-473LF]
464 Ohm [CRT1206-BY- 4640ELF]	47 kOhm [4306M- 101-473]	47 kOhm [4308R- 101-473LF]	47 kOhm [4310R- 102-473]
464 Ohm [CRT1206-BY- 4640ELF]	47 kOhm [4306M- 101-473LF]	47 kOhm [4308R- 102-473]	47 kOhm [4310R- 102-473LF]
4-644456-0	47 kOhm [4306M- 102-473]	47 kOhm [4308R- 102-473LF]	47 kOhm [4416P-1- 473]
46765-1001	47 kOhm [4306M- 102-473LF]	47 kOhm [4309R- 101-473]	47 kOhm [4416P-1- 473LF]
46765-2001			

Multisim 14.1 Education Components

47 kOhm [4416P-2-473]	47 kOhm [4605X-AP1-473LF]	47 kOhm [4608X-102-473LF]	47 kOhm [4612X-101-473LF]
47 kOhm [4416P-2-473LF]	47 kOhm [4606H-102-473LF]	47 kOhm [4608X-AP1-473LF]	47 kOhm [4612X-102-473LF]
47 kOhm [4416P-T01-473]	47 kOhm [4606M-101-473LF]	47 kOhm [4608X-AP2-473LF]	47 kOhm [4614X-101-473LF]
47 kOhm [4416P-T01-473LF]	47 kOhm [4606M-102-473LF]	47 kOhm [4609H-101-473LF]	47 kOhm [4614X-102-473LF]
47 kOhm [4416P-T02-473]	47 kOhm [4606X-101-473LF]	47 kOhm [4609M-101-473LF]	47 kOhm [4814P-1-473]
47 kOhm [4420P-1-473]	47 kOhm [4606X-102-473LF]	47 kOhm [4609X-101-473LF]	47 kOhm [4814P-1-473LF]
47 kOhm [4420P-1-473LF]	47 kOhm [4606X-AP1-473LF]	47 kOhm [4609X-AP1-473LF]	47 kOhm [4814P-2-473]
47 kOhm [4420P-2-473]	47 kOhm [4606X-AP2-473LF]	47 kOhm [4610H-102-473LF]	47 kOhm [4814P-2-473LF]
47 kOhm [4420P-T01-473]	47 kOhm [4607M-101-473LF]	47 kOhm [4610M-101-473LF]	47 kOhm [4814P-T01-473]
47 kOhm [4420P-T02-473]	47 kOhm [4607X-101-473LF]	47 kOhm [4610M-102-473LF]	47 kOhm [4814P-T01-473LF]
47 kOhm [4604H-101-473LF]	47 kOhm [4608H-101-473LF]	47 kOhm [4610X-101-473LF]	47 kOhm [4814P-T02-473]
47 kOhm [4604X-101-473LF]	47 kOhm [4608H-102-473LF]	47 kOhm [4610X-102-473LF]	47 kOhm [4814P-T02-473LF]
47 kOhm [4604X-102-473LF]	47 kOhm [4608M-101-473LF]	47 kOhm [4610X-AP1-473LF]	47 kOhm [4816P-1-473]
47 kOhm [4604X-AP1-473LF]	47 kOhm [4608M-102-473LF]	47 kOhm [4610X-AP2-473LF]	47 kOhm [4816P-1-473LF]
47 kOhm [4605X-101-473LF]	47 kOhm [4608X-101-473LF]	47 kOhm [4611X-101-473LF]	47 kOhm [4816P-2-473]

Multisim 14.1 Education Components

47 kOhm [4816P-2-473LF]	47 kOhm [CAT10-473J4LF]	47 kOhm [CR0402-FX-4702GLF]	47 kOhm [CRM2512-FX-4702ELF]
47 kOhm [4816P-T01-473]	47 kOhm [CAT16-4702F4LF]	47 kOhm [CR0402-JW-473GLF]	47 kOhm [CRM2512-JW-473ELF]
47 kOhm [4816P-T01-473LF]	47 kOhm [CAT16-4702F8LF]	47 kOhm [CR0603-FX-4702ELF]	47 kOhm [CRT0402-DY-4702GLF]
47 kOhm [4816P-T02-473]	47 kOhm [CAT16-473J2LF]	47 kOhm [CR0603-FX-4702HLF]	47 kOhm [CRT0805-BY-4702ELF]
47 kOhm [4816P-T02-473LF]	47 kOhm [CAT16-473J4LF]	47 kOhm [CR0603-JW-473ELF]	47 kOhm [CRT1206-BY-4702ELF]
47 kOhm [4818P-1-473LF]	47 kOhm [CAT16-473J8LF]	47 kOhm [CR0603-JW-473GLF]	47 kOhm [CRT1206-FX-4702ELF]
47 kOhm [4818P-2-473]	47 kOhm [CAT25-473JALF]	47 kOhm [CR0805-FX-4702ELF]	47 kOhm [PWR263S-20-4702JE]
47 kOhm [4818P-2-473LF]	47 kOhm [CAY10-473J4LF]	47 kOhm [CR0805-JW-473ELF]	47 mF [C0805C479KBGAC TU]
47 kOhm [4818P-T01-473]	47 kOhm [CAY16-4702F4LF]	47 kOhm [CR0805-JW-473GLF]	47 mF [C1206C479K1GACT U]
47 kOhm [4818P-T02-473]	47 kOhm [CAY16-473J2LF]	47 kOhm [CR1206-FX-4702ELF]	47 mOhm [CRM1206-FX-R047ELF]
47 kOhm [4820P-1-473]	47 kOhm [CAY16-473J4GLF]	47 kOhm [CR1206-JW-473ELF]	47 mOhm [CRM2010-FX-4702ELF]
47 kOhm [4820P-1-473LF]	47 kOhm [CAY16-473J4LF]	47 kOhm [CR1206-JW-473GLF]	47 kOhm [CRM2010-JW-473ELF]
47 kOhm [4820P-2-473]	47 kOhm [CAY16-473J8LF]	47 kOhm [CR2512-JW-473ELF]	
47 kOhm [4820P-T01-473]	47 kOhm [CAY17-473JALF]		
47 kOhm [4820P-T02-473]	47 kOhm [CR0201-FW-4702GLF]		

Multisim 14.1 Education Components

47 mOhm [CRM2010-JX- R047ELF]	47 nF [06123C473KAT2S]	47 nF [C0603C473K3RACT U]	47 nF [C0805C473M5UAC TU]
47 mOhm [CRM2512-FX- R047ELF]	47 nF [06125C473KAT2W]	47 nF [C0603C473K4RACT U]	47 nF [C0805C473M5VAC TU]
47 mOhm [PWR1913WR047F]	47 nF [0612YC473KAT2S]	47 nF [C0603C473K5NAC TU]	47 nF [C0805F473K3RACT U]
47 mOhm [PWR1913WR047F E]	47 nF [C0402C473K3RACT U]	47 nF [C0603C473K5RACT U]	47 nF [C0805F473K4RACT U]
47 mOhm [PWR2615WR047F]	47 nF [C0402C473K4PACT U]	47 nF [C0603C473K8RACT U]	47 nF [C0805F473K5RACT U]
47 mOhm [PWR2615WR047F E]	47 nF [C0402C473K4RACT U]	47 nF [C0603C473M3VAC TU]	47 nF [C1206C473K1HACT U]
47 mOhm [PWR4525WR047J]	47 nF [C0402C473K8PACT U]	47 nF [C0805C473K1RACT U]	47 nF [C1206C473K1RACT U]
47 nF [03066C473KAT2A]	47 nF [C0402C473K8RACT U]	47 nF [C0805C473K3RACT U]	47 nF [C1206C473K3GACT U]
47 nF [0306YC473KAT2A]	47 nF [C0402C473K9PACT U]	47 nF [C0805C473K4RACT U]	47 nF [C1206C473K3HACT U]
47 nF [0306ZC473KAT2A]	47 nF [C0402C473K9RACT U]	47 nF [C0805C473K5RACT U]	47 nF [C1206C473K3RACT U]
47 nF [05083C473KAT2V]	47 nF [C0603C473K1RACT U]	47 nF [C0805C473K8RACT U]	47 nF [C1206C473K4RACT U]
47 nF [05085C473KAT2A]	47 nF [C0603C473K3NAC TU]		

Multisim 14.1 Education Components

47 nF [C1206C473K5HACT U]	47 nF [C1210C473K2RACT U]	47 nF [C1812C473K5GACT U]	47 nF [GMC7.3472K250K3 1TR12]
47 nF [C1206C473K5RACT U]	47 nF [C1210C473K3GACT U]	47 nF [C1812C473K5HACT U]	47 nF [GMC7.3472K63K31 TR12]
47 nF [C1206C473KARACT U]	47 nF [C1210C473K3HACT U]	47 nF [C1812C473K5RACT U]	47 nF [GMC7.3473K63K31 TR12]
47 nF [C1206C473M5UAC TU]	47 nF [C1210C473K5GACT U]	47 nF [C1825C473K5RACT U]	47 nF [GPC7.3473K63K33 TR12]
47 nF [C1206F473K1RACT U]	47 nF [C1210C473K5HACT U]	47 nF [C2220C473K1GACT U]	47 nF [LG126Z473MAT2S 1]
47 nF [C1206F473K3RACT U]	47 nF [C1210C473K5RACT U]	47 nF [C2220C473K2GACT U]	47 nF [MDC10473K100A5 2P3TUBE]
47 nF [C1206F473K4RACT U]	47 nF [C1210C473KARACT U]	47 nF [C2220C473K5GACT U]	47 nF [MDC10473K250A5 2P3TUBE]
47 nF [C1206F473K5RACT U]	47 nF [C1812C473K1GACT U]	47 nF [CA064C473K4RACT U]	47 nF [MDC10473K400A5 2P3TUBE]
47 nF [C1210C473K1GACT U]	47 nF [C1812C473K1HACT U]	47 nF [CA064C473K8RACT U]	47 nF [MDC10473K50A52 P3TUBE]
47 nF [C1210C473K1HACT U]	47 nF [C1812C473K1RACT U]	47 nF [GMC5.7472K250J3 1TR12]	47 nF [MDC10473K630A5 2P3TUBE]
47 nF [C1210C473K1RACT U]	47 nF [C1812C473K2RACT U]	47 nF [GMC5.7473K50J31 TR12]	47 nF [MDC15473K100B5 3P3TUBE]

Multisim 14.1 Education Components

47 nF [MDC15473K250B5 3P3TUBE]	47 nF [MDS10473K50A52 P3TUBE]	47 nF [PG126Z473MAB2S 1]	47 nF [W2L13C473MAT1S]
47 nF [MDC15473K400B5 3P3TUBE]	47 nF [MDS10473K630A5 2P3TUBE]	47 nF [PG224D473MAB2S 1]	47 nF [W2L1YC473MAT1A]
47 nF [MDC15473K50B53 P3TUBE]	47 nF [MDS15473K100B5 3P3TUBE]	47 nF [PG224W473MAB2 S1]	47 nF [W3F15C4738AT1A]
47 nF [MDC15473K630B5 3P3TUBE]	47 nF [MDS15473K250B5 3P3TUBE]	47 nF [PG224Z473MAB2S 1]	47 nF [W3L1YC473MAT1A]
47 nF [MDK10473K100A5 2P3TUBE]	47 nF [MMC7.3473K100K 31TR12]	47 nF [PG226D473MAB2S 1]	47 Ohm [4114R-1- 470]
47 nF [MDK10473K250A5 2P3TUBE]	47 nF [MMC7.3473K50K3 1TR12]	47 nF [PG226W473MAB2 S1]	47 Ohm [4114R-1- 470LF]
47 nF [MDK10473K400A5 2P3TUBE]	47 nF [PG124D473MAB2S 1]	47 nF [PG226Z473MAB2S 1]	47 Ohm [4114R-2- 470]
47 nF [MDK10473K50A52 P3TUBE]	47 nF [PG124W473MAB2 S1]	47 nF [SPC10.2473K100A 31TR16]	47 Ohm [4114R-2- 470LF]
47 nF [MDS10473K100A5 2P3TUBE]	47 nF [PG124Z473MAB2S 1]	47 nF [SPC10.2473K250A 31TR16]	47 Ohm [4116R-1- 470]
47 nF [MDS10473K250A5 2P3TUBE]	47 nF [PG126D473MAB2S 1]	47 nF [SPC10.2473K250A 31TR16]	47 Ohm [4116R-1- 470LF]
47 nF [MDS10473K400A5 2P3TUBE]	47 nF [PG126W473MAB2 S1]	47 nF [SPC12.7473K400B 31TR24]	47 Ohm [4116R-2- 470]
			47 Ohm [4116R-2- 470LF]
			47 Ohm [4306R- 101-470]
			47 Ohm [4306R- 101-470LF]

Multisim 14.1 Education Components

47 Ohm [4306R-102-470]	47 Ohm [4310R-101-470LF]	47 Ohm [4607X-101-470LF]	47 Ohm [4814P-1-470LF]
47 Ohm [4306R-102-470LF]	47 Ohm [4310R-102-470]	47 Ohm [4608H-102-470LF]	47 Ohm [4814P-2-470]
47 Ohm [4308H-102-470]	47 Ohm [4310R-102-470LF]	47 Ohm [4608M-102-470LF]	47 Ohm [4814P-2-470LF]
47 Ohm [4308H-102-470LF]	47 Ohm [4311R-101-470]	47 Ohm [4608X-101-470LF]	47 Ohm [4814P-T01-470]
47 Ohm [4308R-101-470]	47 Ohm [4416P-1-470]	47 Ohm [4608X-102-470LF]	47 Ohm [4814P-T01-470LF]
47 Ohm [4308R-101-470LF]	47 Ohm [4416P-1-470LF]	47 Ohm [4608X-AP2-470LF]	47 Ohm [4814P-T02-470]
47 Ohm [4308R-102-470]	47 Ohm [4416P-T01-470]	47 Ohm [4609X-101-470LF]	47 Ohm [4816P-1-470]
47 Ohm [4308R-102-470LF]	47 Ohm [4420P-1-470]	47 Ohm [4610H-102-470LF]	47 Ohm [4816P-1-470LF]
47 Ohm [4310H-101-470]	47 Ohm [4420P-T01-470]	47 Ohm [4610X-101-470LF]	47 Ohm [4816P-2-470]
47 Ohm [4310H-101-470LF]	47 Ohm [4420P-T02-470]	47 Ohm [4610X-102-470LF]	47 Ohm [4816P-2-470LF]
47 Ohm [4310M-101-470]	47 Ohm [4604X-102-470LF]	47 Ohm [4610X-AP1-470LF]	47 Ohm [4816P-T01-470]
47 Ohm [4310M-101-470LF]	47 Ohm [4605X-101-470LF]	47 Ohm [4612X-102-470LF]	47 Ohm [4816P-T01-470LF]
47 Ohm [4310M-102-470]	47 Ohm [4606H-102-470LF]	47 Ohm [4613X-101-470LF]	47 Ohm [4816P-T02-470]
47 Ohm [4310M-102-470LF]	47 Ohm [4606X-101-470LF]	47 Ohm [4614X-102-470LF]	47 Ohm [4816P-T02-470LF]
47 Ohm [4310R-101-470]	47 Ohm [4606X-102-470LF]	47 Ohm [4814P-1-470]	47 Ohm [4820P-1-470]

Multisim 14.1 Education Components

47 Ohm [4820P-T01-470]	47 Ohm [CR0201-FW-47R0GLF]	47 Ohm [CRM1206-JW-470ELF]	47 Ohm [PWR163S-25-47R0F]
47 Ohm [CAT10-470J4LF]	47 Ohm [CR0402-FX-47R0GLF]	47 Ohm [CRM2512-JW-470ELF]	47 Ohm [PWR163S-25-47R0FE]
47 Ohm [CAT16-470J2LF]	47 Ohm [CR0402-JW-470GLF]	47 Ohm [CRS2010-FX-47R0ELF]	47 Ohm [PWR163S-25-47R0J]
47 Ohm [CAT16-470J4LF]	47 Ohm [CR0603-FX-47R0ELF]	47 Ohm [CRS2512-FX-47R0ELF]	47 Ohm [PWR163S-25-47R0JE]
47 Ohm [CAT16-470J8LF]	47 Ohm [CR0603-FX-47R0HLF]	47 Ohm [CRT0603-FY-47R0ELF]	47 Ohm [PWR2010W47R0E]]
47 Ohm [CAT16-47R0F4LF]	47 Ohm [CR0603-JW-470ELF]	47 Ohm [CRT0805-BW-47R0ELF]	47 Ohm [PWR220T-20-47R0F]
47 Ohm [CAT16-47R0F8LF]	47 Ohm [CR0603-JW-470GLF]	47 Ohm [CRT0805-BY-47R0ELF]	47 Ohm [PWR220T-20-47R0J]
47 Ohm [CAT25-470JALF]	47 Ohm [CR0805-FX-47R0ELF]	47 Ohm [CRT0805-CV-47R0ELF]	47 Ohm [PWR220T-35-47R0F]
47 Ohm [CAY10-470J2LF]	47 Ohm [CR0805-FX-47R0GLF]	47 Ohm [CRT1206-CW-47R0ELF]	47 Ohm [PWR220T-35-47R0J]
47 Ohm [CAY10-470J4LF]	47 Ohm [CR0805-JW-470ELF]	47 Ohm [FW10A47R0JA]	47 Ohm [PWR220T-30-47R0F]
47 Ohm [CAY16-470J2LF]	47 Ohm [CR1206-FX-47R0ELF]	47 Ohm [FW20A47R0JA]	47 Ohm [PWR221T-30-47R0F]
47 Ohm [CAY16-470J4LF]	47 Ohm [CR1206-JW-470ELF]	47 Ohm [FW30A47R0JA]	47 Ohm [PWR221T-30-47R0J]
47 Ohm [CAY16-470J8LF]	47 Ohm [CR2010-FX-47R0ELF]	47 Ohm [FW50A47R0JA]	47 Ohm [PWR221T-30-47R0J]
47 Ohm [CAY16-47R0F4LF]	47 Ohm [CR2512-JW-470ELF]	47 Ohm [FW70A47R0JA]	
47 Ohm [CAY17-470JALF]	47 Ohm [CRM1206-FX-47R0ELF]		

Multisim 14.1 Education Components

47 Ohm [PWR2615W47R0F]	47 Ohm [PWR3014W47R0JE]	47 pF [C0402C470K5GACT U]	47 pF [C1206C470K1GACT U]
47 Ohm [PWR2615W47R0J]	47 Ohm [PWR4318W47R0JE]	47 pF [C0402C470K8GACT U]	47 pF [C1206C470K2GACT U]
47 Ohm [PWR2615W47R0JE]	47 Ohm [PWR4525W47R0J]	47 pF [C0603C470K1GACT U]	47 pF [C1206C470K3GACT U]
47 Ohm [PWR263S-20- 47R0F]	47 Ohm [PWR4525W47R0JE]	47 pF [C0603C470K5GACT U]	47 pF [C1206C470K5GACT U]
47 Ohm [PWR263S-20- 47R0FE]	47 Ohm [PWR5322W47R0JE]	47 pF [C0603C470K8GACT U]	47 pF [C1206C470KBGAC TU]
47 Ohm [PWR263S-20- 47R0J]	47 Ohm [PWR6327W47R0J]	47 pF [C0805C470K1GACT U]	47 pF [C1206C470KDGAC TU]
47 Ohm [PWR263S-20- 47R0JE]	47 Ohm [PWR6327W47R0JE]	47 pF [C0805C470K2GACT U]	47 pF [C1206C470KFGACT U]
47 Ohm [PWR263S-35- 47R0F]	47 Ohm [WS1A47R0J]	47 pF [C0805C470K3GACT U]	47 pF [C1206C470KGGAC TU]
47 Ohm [PWR263S-35- 47R0FE]	47 pF [C0201C470K3GACT U]	47 pF [C0805C470K5GACT U]	47 pF [C1210C470K5GACT U]
47 Ohm [PWR263S-35- 47R0J]	47 pF [C0402C470K3GACT U]	47 pF [C0805C470KBGAC TU]	47 pF [C1210C470KBGAC TU]
47 Ohm [PWR263S-35- 47R0JE]	47 pF [C0402C470K4GACT U]	47 pF [C0805C470KCGAC TU]	47 pF [C1812C470KBGAC TU]
47 Ohm [PWR3014W47R0F E]			

Multisim 14.1 Education Components

47 pF [C1812C470KDGAC TU]	47 uF [16TQC47MYFD]	47 uF [EEFCT1D470R]	47 uF [T491B476M010AT]
47 pF [C1825C470KBGAC TU]	47 uF [16TQC47MYFT]	47 uF [EEFCX1A470R]	47 uF [T491C476M004AT]
47 pF [C2220C470KBGAC TU]	47 uF [20SVP47M]	47 uF [EEFCX1C470R]	47 uF [T491C476M006AT]
47 pF [C2225C470KBGAC TU]	47 uF [20TQC47MYF]	47 uF [EEFCX1D470R]	47 uF [T491C476M010AT]
47 pF [C2225C470KBGAC TU]	47 uF [20TQC47MYFT]	47 uF [EEFHX1A470R]	47 uF [T491C476M016AT]
47 pF [CA064C470K3GAC TU]	47 uF [2R5TPU47MSI]	47 uF [EEFHX1C470R]	47 uF [T491C476M020AT]
47 pF [CA064C470K5GAC TU]	47 uF [6TPC47M]	47 uF [EEFHX1D470R]	47 uF [T491D476M006AT]
47 pF [CA064C470K8GAC TU]	47 uF [6TPH47MHA]	47 uF [EEHZA1V470P]	47 uF [T491D476M010AT]
47 pF [CA064C470K8GAC TU]	47 uF [6TPU47MSI]	47 uF [EEHZC1V470P]	47 uF [T491D476M016AT]
47 pF [W2F11A4708AT1A]	47 uF [8TPG47M]	47 uF [T409H476M010AH 4250]	47 uF [T491D476M020AT]
47 pF [W3F11A4708AT1A]	47 uF [A700V476M006AT E018]	47 uF [T419F476M010AH 4250]	47 uF [T491D476M025AT]
47 uF [10TPB47M]	47 uF [A700V476M006AT E025]	47 uF [T491A476M004AT]	47 uF [T491E476M035AT]
47 uF [10TPE47MAZB]	47 uF [A700V476M006AT E028]	47 uF [T491A476M006AT]	47 uF [T491T476M004AT]
47 uF [10TPG47M]	47 uF [EEFCS1A470R]	47 uF [T491B476M004AT]	
47 uF [16TQC47MW]	47 uF [EEFCT1C470R]	47 uF [T491B476M006AT]	

Multisim 14.1 Education Components

47 uF [T491T476M006AT]	47 uF [T494C476M006AT]	47 uF [T494U476M006AT]	47 uF [T495D476M016AT E080]
47 uF [T491U476M004AT]	47 uF [T494C476M010AT]	47 uF [T494U476M010AT]	47 uF [T495D476M016AT E100]
47 uF [T491U476M006AT]	47 uF [T494C476M016AT]	47 uF [T494V476M010AT]	47 uF [T495D476M016AT E150]
47 uF [T491U476M010AT]	47 uF [T494D476M006AT]	47 uF [T494V476M016AT]	47 uF [T495D476M020AT E100]
47 uF [T491V476M010AT]	47 uF [T494D476M010AT]	47 uF [T494X476M025AT]	47 uF [T495D476M020AT E175]
47 uF [T491V476M016AT]	47 uF [T494D476M016AT]	47 uF [T495B476M006AT E450]	47 uF [T495D476M025AT E120]
47 uF [T491X476M025AT]	47 uF [T494D476M020AT]	47 uF [T495B476M010AT E500]	47 uF [T495D476M025AT E250]
47 uF [T491X476M035AT]	47 uF [T494D476M025AT]	47 uF [T495C476M016AT E350]	47 uF [T495V476M006AT E150]
47 uF [T494A476M004AT]	47 uF [T494E476M035AT]	47 uF [T495D476M010AT E080]	47 uF [T495X476M020AT E065]
47 uF [T494B476M004AT]	47 uF [T494T476M004AT]	47 uF [T495D476M010AT E090]	47 uF [T495X476M020AT E100]
47 uF [T494B476M006AT]	47 uF [T494T476M006AT]	47 uF [T495D476M010AT E200]	47 uF [T495X476M020AT E150]
47 uF [T494B476M010AT]			
47 uF [T494C476M004AT]			

Multisim 14.1 Education Components

47 uF [T495X476M025AT E080]	47 uF [T510E476M035AT E050]	47 uF [T520B476M008AT E035]	47 uF [T520V476M016AT E045]
47 uF [T495X476M025AT E150]	47 uF [T510X476M035AT E055]	47 uF [T520B476M008AT E070]	47 uF [T520V476M016AT E070]
47 uF [T495X476M025AT E185]	47 uF [T510X476M035AT E065]	47 uF [T520B476M010AT E035]	47 uF [T520W476M016AT E045]
47 uF [T495X476M025AT E200]	47 uF [T520A476M004AT E070]	47 uF [T520B476M010AT E070]	47 uF [T521D476M020AT E055]
47 uF [T495X476M035AT E185]	47 uF [T520A476M004AT E080]	47 uF [T520C476M010AT E100]	47 uF [T521V476M020AT E090]
47 uF [T495X476M035AT E200]	47 uF [T520A476M006AT E150]	47 uF [T520D476M016AT E035]	47 uF [T521W476M020AT E045]
47 uF [T495X476M035AT E300]	47 uF [T520A476M2R5AT E090]	47 uF [T520D476M016AT E070]	47 uF [T521X476M035AT E030]
47 uF [T497G476M006AT 6110]	47 uF [T520B476M006AT E025]	47 uF [T520Q476M011AT E040]	47 uF [T521X476M035AT E070]
47 uF [T498C476M006AT E800]	47 uF [T520B476M006AT E035]	47 uF [T520T476M004AT E070]	47 uF [T525B476M006AT E080]
47 uF [T498D476M010AT E600]	47 uF [T520B476M006AT E040]	47 uF [T520T476M006AT E040]	47 uF [T525D476M016AT E035]
47 uF [T498D476M016AT E600]	47 uF [T520B476M006AT E070]	47 uF [T520T476M006AT E070]	47 uF [T525D476M016AT E065]

Multisim 14.1 Education Components

47 uF [T525T476M006AT E080]	47 uF [TAJC476K016RNJ]	47 uF [TAJX476K020RNJ]	47 uF [TPSB476K006R025 0]
47 uF [T543A476M004AT E080]	47 uF [TAJC476K020RNJ]	47 uF [TAJY476K010RNJ]	47 uF [TPSB476K006R035 0]
47 uF [T543W476M016AT E045]	47 uF [TAJD476K010RNJ]	47 uF [TAJY476K016RNJ]	47 uF [TPSB476K006R050 0]
47 uF [TACR476K002RTA]	47 uF [TAJD476K020RNJ]	47 uF [TAJY476K025RNJ]	47 uF [TPSB476K010R035 0]
47 uF [TACR476K003RTA]	47 uF [TAJD476K025RNJ]	47 uF [THJC476K006RJN]	47 uF [TPSB476K010R050 0]
47 uF [TACR476K004RTA]	47 uF [TAJE476K020RNJ]	47 uF [THJC476K010RJN]	47 uF [TPSB476K010R065 0]
47 uF [TAJA476K002RNJ]	47 uF [TAJE476K025RNJ]	47 uF [THJC476K016RJN]	47 uF [TPSC476K006R030 0]
47 uF [TAJA476K004RNJ]	47 uF [TAJE476K035RNJ]	47 uF [TPMD476K020R00 45]	47 uF [TPSC476K010R035 0]
47 uF [TAJA476K006RNJ]	47 uF [TAJT476K006RNJ]	47 uF [TPMD476K020R00 55]	47 uF [TPSC476K016R011 0]
47 uF [TAJB476K004RNJ]	47 uF [TAJV476K035RNJ]	47 uF [TPME476K035R00 65]	47 uF [TPSA476K004R050 0]
47 uF [TAJB476K006RNJ]	47 uF [TAJW476K010RNJ]		
47 uF [TAJB476K010RNJ]	47 uF [TAJW476K016RNJ]		
47 uF [TAJC476K006RNJ]	47 uF [TAJX476K016RNJ]		
47 uF [TAJC476K010RNJ]			

Multisim 14.1 Education Components

47 uF [TPSD476K016R008 0]	47 uF [TPSE476K020R020 0]	47 uF [TRJC476K010RRJ]	47 uH [SDR0703- 470KL]
47 uF [TPSD476K016R010 0]	47 uF [TPSE476K020R025 0]	47 uF [TRJC476K016RRJ]	47 uH [SDR0805- 470KL]
47 uF [TPSD476K016R015 0]	47 uF [TPSE476K025R008 0]	47 uF [TRJD476K020RRJ]	47 uH [SDR0906- 470KL]
47 uF [TPSD476K016R020 0]	47 uF [TPSE476K025R010 0]	47 uF [TRMD476K020R00 55]	47 uH [SDR1005- 470KL]
47 uF [TPSD476K020R010 0]	47 uF [TPSE476K025R012 5]	47 uF [TRME476K025R00 65]	47 uH [SDR1006- 470KL]
47 uF [TPSD476K020R020 0]	47 uF [TPSE476K035R020 0]	47 uH [SDE0403A- 470K]	47 uH [SDR1030- 470M]
47 uF [TPSD476K025R015 0]	47 uF [TPSE476K035R025 0]	47 uH [SDE0604A- 470M]	47 uH [SDR1045- 470M]
47 uF [TPSD476K025R025 0]	47 uF [TPSW476K010R01 25]	47 uH [SDE0805A- 470K]	47 uH [SDR1105- 470KL]
47 uF [TPSE476K020R007 0]	47 uF [TPSW476K010R01 50]	47 uH [SDE1006A- 470K]	47 uH [SDR1305- 470M]
47 uF [TPSE476K020R012 5]	47 uF [TPSW476K010R02 50]	47 uH [SDR0302- 470KL]	47 uH [SDR1307- 470KL]
47 uF [TPSE476K020R015 0]	47 uF [TPSY476K016R025 0]	47 uH [SDR0403- 470KL]	47 uH [SDR1307A- 470K]
		47 uH [SDR0503- 470KL]	47 uH [SDR1806- 470ML]
		47 uH [SDR0603- 470KL]	47 uH [SDR6603- 470M]
		47 uH [SDR0604- 470KL]	47 uH [SDR7030- 470K]

Multisim 14.1 Education Components

47 uH [SRN1060-470M]	47 uH [SRR0604-470KL]	47 uH [SRR1240-470M]	47 uH [SRR7032-470M]
47 uH [SRN3010-470M]	47 uH [SRR0618-470ML]	47 uH [SRR1260-470M]	47 uH [SRR7045-470M]
47 uH [SRN3015-470M]	47 uH [SRR0735A-470M]	47 uH [SRR1260A-470M]	47 uH [SRU1028-470Y]
47 uH [SRN4018-470M]	47 uH [SRR0745A-470M]	47 uH [SRR1280-470M]	47 uH [SRU1028A-470Y]
47 uH [SRN4026-470M]	47 uH [SRR0804-470K]	47 uH [SRR1806-470M]	47 uH [SRU1038-470Y]
47 uH [SRN5040-470M]	47 uH [SRR0805-470Y]	47 uH [SRR3011-470YL]	47 uH [SRU1038A-470Y]
47 uH [SRN6028-470M]	47 uH [SRR0905-470Y]	47 uH [SRR4011-470YL]	47 uH [SRU1048-470Y]
47 uH [SRN6045-470M]	47 uH [SRR0906-470ML]	47 uH [SRR4018-470Y]	47 uH [SRU1048A-470Y]
47 uH [SRN8040-470M]	47 uH [SRR0908-470ML]	47 uH [SRR4028-470Y]	47 uH [SRU1063-470Y]
47 uH [SRP1038A-470M]	47 uH [SRR1003-470M]	47 uH [SRR5018-470Y]	47 uH [SRU2013-470Y]
47 uH [SRP1265A-470M]	47 uH [SRR1005-470Y]	47 uH [SRR5028-470Y]	47 uH [SRU2016-470Y]
47 uH [SRP1770TA-470M]	47 uH [SRR1206-470YL]	47 uH [SRR6028-470Y]	47 uH [SRU3017-470Y]
47 uH [SRP6540-470M]	47 uH [SRR1208-470YL]	47 uH [SRR6038-470Y]	47 uH [SRU3028-470Y]
47 uH [SRP7050TA-470M]	47 uH [SRR1210-470M]	47 uH [SRR6040A-470M]	47 uH [SRU5011-470Y]
47 uH [SRR0603-470KL]	47 uH [SRR1210A-470M]	47 uH [SRR6603-470ML]	47 uH [SRU5016-470Y]

Multisim 14.1 Education Components

47 uH [SRU5018-470Y]	47.5 kOhm [CR1206-FX-4752ELF]	470 kOhm [4114R-1-474LF]	470 kOhm [4309R-101-474]
47 uH [SRU5028-470Y]	47.5 kOhm [CR2512-FX-4752ELF]	470 kOhm [4114R-2-474]	470 kOhm [4309R-101-474LF]
47 uH [SRU5028A-470Y]	47.5 kOhm [CRT0603-BY-4752ELF]	470 kOhm [4116R-1-474]	470 kOhm [4310R-101-474]
47 uH [SRU6011-470Y]	47.5 kOhm [CRT0805-FX-4752ELF]	470 kOhm [4116R-1-474LF]	470 kOhm [4310R-101-474LF]
47 uH [SRU6018-470Y]	47.5 kOhm [CRT0805-FX-4752ELF]	470 kOhm [4116R-2-474]	470 kOhm [4310R-102-474]
47 uH [SRU6025-470Y]	47.5 Ohm [CAT16-47R5F4LF]	470 kOhm [4116R-2-474LF]	470 kOhm [4310R-102-474LF]
47 uH [SRU6025A-470Y]	47.5 Ohm [CAY16-47R5F4LF]	470 kOhm [4306M-102-474LF]	470 kOhm [4604X-101-474LF]
47 uH [SRU8028-470Y]	47.5 Ohm [CR0402-FX-47R5GLF]	470 kOhm [4306R-101-474]	470 kOhm [4604X-102-474LF]
47 uH [SRU8028A-470Y]	47.5 Ohm [CR0603-FX-47R5ELF]	470 kOhm [4306R-101-474LF]	470 kOhm [4605X-101-474LF]
47 uH [SRU8043-470Y]	47.5 Ohm [CR0805-FX-47R5ELF]	470 kOhm [4306R-102-474]	470 kOhm [4606X-101-474LF]
47.5 kOhm [CAY16-4752F4LF]	47.5 Ohm [CR1206-FX-47R5ELF]	470 kOhm [4306R-102-474LF]	470 kOhm [4606X-102-474LF]
47.5 kOhm [CR0402-FX-4752GLF]	47.5 Ohm [CRM1206-FX-47R5ELF]	470 kOhm [4308R-101-474]	470 kOhm [4607X-101-474LF]
47.5 kOhm [CR0603-FX-4752ELF]	47.5 Ohm [CRT0603-FZ-47R5ELF]	470 kOhm [4308R-101-474LF]	470 kOhm [4608H-102-474LF]
47.5 kOhm [CR0805-FX-4752ELF]	470 kOhm [4114R-1-474]	470 kOhm [4308R-102-474]	470 kOhm [4608M-101-474LF]
		470 kOhm [4308R-102-474LF]	470 kOhm [4608X-101-474LF]

Multisim 14.1 Education Components

470 kOhm [4608X-102-474LF]	470 kOhm [CAT16-474J4LF]	470 kOhm [CR0603-JW-474ELF]	470 mOhm [CRL0603-FW-R470ELF]
470 kOhm [4608X-AP2-474LF]	470 kOhm [CAT25-474JALF]	470 kOhm [CR0805-FX-4703ELF]	470 mOhm [CRL0603-JW-R470ELF]
470 kOhm [4609X-101-474LF]	470 kOhm [CAY10-474J4LF]	470 kOhm [CR0805-JW-474ELF]	470 mOhm [CRL0805-FW-R470ELF]
470 kOhm [4610X-101-474LF]	470 kOhm [CAY16-4703F4LF]	470 kOhm [CR0805-JW-474GLF]	470 mOhm [CRL0805-JW-R470ELF]
470 kOhm [4610X-102-474LF]	470 kOhm [CAY16-474J2LF]	470 kOhm [CR1206-FX-4703ELF]	470 mOhm [CRL1206-FW-R470ELF]
470 kOhm [4816P-1-474]	470 kOhm [CAY16-474J4LF]	470 kOhm [CR1206-FX-4703GLF]	470 mOhm [CRL1206-JW-R470ELF]
470 kOhm [4816P-1-474LF]	470 kOhm [CAY16-474J8LF]	470 kOhm [CR1206-JW-474ELF]	470 mOhm [CRL2010-FW-R470ELF]
470 kOhm [4816P-2-474]	470 kOhm [CHV0805-JW-474ELF]	470 kOhm [CRM1206-FX-4703ELF]	470 mOhm [CRL2010-JW-R470ELF]
470 kOhm [4816P-2-474LF]	470 kOhm [CHV2010-FW-4703ELF]	470 kOhm [CRM1206-JW-474ELF]	470 mOhm [CRL2512-FW-R470ELF]
470 kOhm [4816P-T01-474]	470 kOhm [CR0201-JW-474GLF]	470 kOhm [CRM2010-JW-474ELF]	470 mOhm [CRL2512-JW-R470ELF]
470 kOhm [4816P-T01-474LF]	470 kOhm [CR0402-FX-4703GLF]	470 kOhm [CRM2010-JW-474ELF]	
470 kOhm [4816P-T02-474]	470 kOhm [CR0402-JW-474GLF]		
470 kOhm [4816P-T02-474LF]			
470 kOhm [4820P-T01-474]			
470 kOhm [CAT16-4703F4LF]	470 kOhm [CR0603-FX-4703ELF]	470 kOhm [CRT0805-CX-4703ELF]	470 mOhm [CRM1206-FX-R470ELF]

Multisim 14.1 Education Components

470 mOhm [CRM2010-FX- R470ELF]	470 nF [05086C474KAT2V]	470 nF [C0805C474K3PACT U]	470 nF [C1206C474K8RACT U]
470 mOhm [CRM2512-FX- R470ELF]	470 nF [0508ZC474KAT2V] 470 nF [0612YC474KAT2V]	470 nF [C0805C474K3RACT U]	470 nF [C1206C474M3VAC TU]
470 mOhm [CRM2512-JX- R470ELF]	470 nF [0612ZC474KAT2S]	470 nF [C0805C474K4RACT U]	470 nF [C1206C474M4VAC TU]
470 mOhm [PWR1913WR470J]	470 nF [C0402C474K9PACT U]	470 nF [C0805C474K8RACT U]	470 nF [C1206F474K3RACT U]
470 mOhm [PWR1913WR470JE]	470 nF [C0603C474K4PACT U]	470 nF [C0805C474M3VAC TU]	470 nF [C1206F474K4RACT U]
470 mOhm [PWR2615WR470J]	470 nF [C0603C474K4RACT U]	470 nF [C0805C474M4VAC TU]	470 nF [C1210C474K3RACT U]
470 mOhm [PWR2615WR470JE]	470 nF [C0603C474K8PACT U]	470 nF [C1206C474K3NAC TU]	470 nF [C1210C474K4RACT U]
470 mOhm [PWR4318WR470JE]	470 nF [C0603C474K8RACT U]	470 nF [C1206C474K3RACT U]	470 nF [C1210C474K5RACT U]
470 mOhm [PWR4525WR470J]	470 nF [C0603C474K9PACT U]	470 nF [C1206C474K4RACT U]	470 nF [C1210C474M5UAC TU]
470 mOhm [PWR4525WR470JE]	470 nF [C0603C474K9RACT U]	470 nF [C1206C474K5NAC TU]	470 nF [C1210F474K1RACT U]
470 mOhm [PWR6327WR470J]	470 nF [C0805C474K3NAC TU]	470 nF [C1206C474K5RACT U]	470 nF [C1210F474K3RACT U]

Multisim 14.1 Education Components

470 nF [C1210F474K4RACT U]	470 nF [C2220C474K1RACT U]	470 nF [MDC10474K100A5 2P3TUBE]	470 nF [MDS10474K250A5 2P3TUBE]
470 nF [C1210F474K5RACT U]	470 nF [C2220C474K5RACT U]	470 nF [MDC10474K250A5 2P3TUBE]	470 nF [MDS10474K50A52 P3TUBE]
470 nF [C1812C474K5RACT U]	470 nF [C2220C474KARACT U]	470 nF [MDC10474K400A5 8P7TUBE]	470 nF [MDS15474K100B5 3P3TUBE]
470 nF [C1812C474KARACT U]	470 nF [C2225C474K1RACT U]	470 nF [MDC10474K400A5 8P8TUBE]	470 nF [MDS15474K250B5 3P3TUBE]
470 nF [C1812C474M5UAC TU]	470 nF [C2225C474K2RACT U]	470 nF [MDC10474K50A52 P3TUBE]	470 nF [PG224D474MAB2S 1]
470 nF [C1812F474K1RACT U]	470 nF [C2225C474K5RACT U]	470 nF [MDC15474K100B5 3P3TUBE]	470 nF [PG224W474MAB2 S1]
470 nF [C1812F474K3RACT U]	470 nF [C2225C474KARACT U]	470 nF [MDC15474K250B5 3P3TUBE]	470 nF [PG224Z474MAB2S 1]
470 nF [C1812F474K5RACT U]	470 nF [C2225C474M1UAC TU]	470 nF [MDC15474K50B53 P3TUBE]	470 nF [SPC16.5474K100C 31TR24]
470 nF [C1825C474K1RACT U]	470 nF [CDR06BX474AKSM]	470 nF [MDK10474K250A5 2P3TUBE]	470 nF [T491A474M025AT]
470 nF [C1825C474K5RACT U]	470 nF [LDECD3470KA5N0 0]	470 nF [MDK10474K50A52 P3TUBE]	470 nF [T491A474M035AT]
470 nF [C1825C474KARACT U]	470 nF [LG224Z474MAT2S 1]	470 nF [MDS10474K100A5 2P3TUBE]	470 nF [T491B474M035AT]
			470 nF [T491B474M050AT]

Multisim 14.1 Education Components

470 nF [T491C474M050AT]	470 nF [TAJR474K025RNJ]	470 nF [W2L1ZC474MAT1S]	470 nH [SRP4012- R47M]
470 nF [T494A474M025AT]	470 nF [TAJR474K035RNJ]	470 nF [W3L1YC474MAT1A]	470 nH [SRP4012TA-R47M]
470 nF [T494A474M035AT]	470 nF [TAJS474K020RNJ]	470 nF [W3L1ZC474MAT1S]	470 nH [SRP4020- R47M]
470 nF [T494B474M035AT]	470 nF [TAJS474K025RNJ]	470 nH [SRN2010- R47M]	470 nH [SRP4020TA-R47M]
470 nF [T494B474M050AT]	470 nF [TAJS474K035RNJ]	470 nH [SRN2012- R47M]	470 nH [SRP5015TA-R47M]
470 nF [T494C474M050AT]	470 nF [TAJT474K035RNJ]	470 nH [SRN2510- R47M]	470 nH [SRP5030TA-R47M]
470 nF [T498A474M025AT E8K5]	470 nF [THJA474K025RJN]	470 nH [SRN2512- R47M]	470 nH [SRP5030T- R47M]
470 nF [TACL474K016RTA]	470 nF [TPSA474K025R700 0]	470 nH [SRP1040- R47M]	470 nH [SRP7028A- R47M]
470 nF [TAJA474K025RNJ]	470 nF [TPSA474K035R600 0]	470 nH [SRP1235- R47M]	470 nH [SRP7030- R47FM]
470 nF [TAJA474K035RNJ]	470 nF [TPSB474K035R400 0]	470 nH [SRP1245A- R47M]	470 nH [SRP7050TA-R47M]
470 nF [TAJA474K050RNJ]	470 nF [TPSC474K050R230 0]	470 nH [SRP1250- R47M]	470 nH [SRR4011- R47YL]
470 nF [TAJB474K035RNJ]	470 nF [W2L1ZC474MAT1A]	470 nH [SRP1265A- R47M]	470 Ohm [4114R-1- 471]
470 nF [TAJC474K050RNJ]		470 nH [SRP1270- R47M]	470 Ohm [4114R-1- 471LF]
470 nF [TAJR474K020RNJ]			470 Ohm [4114R-2- 471LF]

Multisim 14.1 Education Components

470 Ohm [4116R-1-471]	470 Ohm [4308H-101-471LF]	470 Ohm [4310H-102-471LF]	470 Ohm [4420P-2-471]
470 Ohm [4116R-1-471LF]	470 Ohm [4308H-102-471]	470 Ohm [4310M-101-471]	470 Ohm [4420P-T01-471]
470 Ohm [4116R-2-471]	470 Ohm [4308H-102-471LF]	470 Ohm [4310M-101-471LF]	470 Ohm [4420P-T02-471]
470 Ohm [4116R-2-471LF]	470 Ohm [4308M-101-471]	470 Ohm [4310M-102-471]	470 Ohm [4604X-101-471LF]
470 Ohm [4304M-102-471]	470 Ohm [4308M-102-471]	470 Ohm [4310M-102-471LF]	470 Ohm [4604X-102-471LF]
470 Ohm [4304M-102-471LF]	470 Ohm [4308M-102-471LF]	470 Ohm [4310R-101-471]	470 Ohm [4605H-101-471LF]
470 Ohm [4306H-101-471]	470 Ohm [4308R-101-471]	470 Ohm [4310R-101-471LF]	470 Ohm [4605M-101-471LF]
470 Ohm [4306H-101-471LF]	470 Ohm [4308R-101-471LF]	470 Ohm [4310R-102-471]	470 Ohm [4605X-101-471LF]
470 Ohm [4306H-102-471]	470 Ohm [4308R-102-471]	470 Ohm [4310R-102-471LF]	470 Ohm [4605X-AP1-471LF]
470 Ohm [4306H-102-471LF]	470 Ohm [4308R-102-471LF]	470 Ohm [4416P-1-471]	470 Ohm [4606M-101-471LF]
470 Ohm [4306R-101-471]	470 Ohm [4309R-101-471]	470 Ohm [4416P-1-471LF]	470 Ohm [4606M-102-471LF]
470 Ohm [4306R-101-471LF]	470 Ohm [4309R-101-471LF]	470 Ohm [4416P-2-471]	470 Ohm [4606X-101-471LF]
470 Ohm [4306R-102-471]	470 Ohm [4310H-101-471]	470 Ohm [4416P-T01-471]	470 Ohm [4606X-102-471LF]
470 Ohm [4306R-102-471LF]	470 Ohm [4310H-101-471LF]	470 Ohm [4416P-T02-471]	470 Ohm [4606X-AP1-471LF]
470 Ohm [4308H-101-471]	470 Ohm [4310H-102-471]	470 Ohm [4420P-1-471]	470 Ohm [4606X-AP2-471LF]

Multisim 14.1 Education Components

470 Ohm [4607X-101-471LF]	470 Ohm [4610M-101-471LF]	470 Ohm [4814P-T01-471LF]	470 Ohm [4820P-2-471LF]
470 Ohm [4608H-101-471LF]	470 Ohm [4610X-101-471LF]	470 Ohm [4814P-T02-471]	470 Ohm [4820P-T01-471]
470 Ohm [4608H-102-471LF]	470 Ohm [4610X-102-471LF]	470 Ohm [4814P-T02-471LF]	470 Ohm [4820P-T01-471LF]
470 Ohm [4608M-101-471LF]	470 Ohm [4610X-AP1-471LF]	470 Ohm [4816P-1-471]	470 Ohm [4820P-T02-471]
470 Ohm [4608M-102-471LF]	470 Ohm [4611X-101-471LF]	470 Ohm [4816P-1-471F]	470 Ohm [CAT10-471J4LF]
470 Ohm [4608X-101-471LF]	470 Ohm [4612H-101-471LF]	470 Ohm [4816P-1-471LF]	470 Ohm [CAT16-4700F4LF]
470 Ohm [4608X-102-471LF]	470 Ohm [4612M-101-471LF]	470 Ohm [4816P-2-471]	470 Ohm [CAT16-471J4LF]
470 Ohm [4608X-AP1-471LF]	470 Ohm [4612X-101-471LF]	470 Ohm [4816P-2-471LF]	470 Ohm [CAT16-471J8LF]
470 Ohm [4608X-AP2-471LF]	470 Ohm [4612X-102-471LF]	470 Ohm [4816P-T01-471]	470 Ohm [CAT25-471JALF]
470 Ohm [4609H-101-471LF]	470 Ohm [4614X-102-471LF]	470 Ohm [4816P-T01-471LF]	470 Ohm [CAY10-471J2LF]
470 Ohm [4609M-101-471LF]	470 Ohm [4814P-1-471]	470 Ohm [4816P-T02-471]	470 Ohm [CAY10-471J4LF]
470 Ohm [4609X-101-471LF]	470 Ohm [4814P-1-471LF]	470 Ohm [4816P-T02-471LF]	470 Ohm [CAY16-4700F4LF]
470 Ohm [4609X-AP1-471LF]	470 Ohm [4814P-2-471]	470 Ohm [4818P-T01-471]	470 Ohm [CAY16-471J2LF]
470 Ohm [4610H-101-471LF]	470 Ohm [4814P-2-471LF]	470 Ohm [4820P-1-471]	470 Ohm [CAY16-471J4LF]
470 Ohm [4610H-102-471LF]	470 Ohm [4814P-T01-471]	470 Ohm [4820P-2-471]	470 Ohm [CAY16-471J8LF]

Multisim 14.1 Education Components

470 Ohm [CAY17-471JALF]	470 Ohm [CRM1206-JW-471ELF]	470 Ohm [PWR263S-20-4700F]	470 pF [C0402C471K3GACT U]
470 Ohm [CR0201-JW-471GLF]	470 Ohm [CRM2010-JW-471ELF]	470 Ohm [PWR263S-20-4700J]	470 pF [C0402C471K3HACT U]
470 Ohm [CR0402-FX-4700GLF]	470 Ohm [CRM2512-FX-4700ELF]	470 Ohm [PWR263S-20-4700JE]	470 pF [C0402C471K3RACT U]
470 Ohm [CR0603-FX-4700ELF]	470 Ohm [CRM2512-JW-471ELF]	470 Ohm [PWR263S-35-4700F]	470 pF [C0402C471K4RACT U]
470 Ohm [CR0603-JW-471ELF]	470 Ohm [CRT0805-BY-4700ELF]	470 Ohm [PWR263S-35-4700J]	470 pF [C0402C471K5HACT U]
470 Ohm [CR0805-FX-4700ELF]	470 Ohm [PWR163S-25-4700J]	470 Ohm [PWR4318W4700JE]	470 pF [C0402C471K5RACT U]
470 Ohm [CR0805-FX-4700GLF]	470 Ohm [PWR220T-20-4700F]	470 Ohm [PWR4525W4700J]	470 pF [C0402C471K8RACT U]
470 Ohm [CR0805-JW-471ELF]	470 Ohm [PWR220T-20-4700J]	470 Ohm [PWR4525W4700JE]	470 pF [C0402C471K9RACT U]
470 Ohm [CR0805-JW-471GLF]	470 Ohm [PWR220T-35-4700J]	470 Ohm [PWR5322W4700JE]	470 pF [C0603C471K1HACT U]
470 Ohm [CR1206-FX-4700ELF]	470 Ohm [PWR2615W4700J]	470 Ohm [PWR6327W4700J]	470 pF [C0603C471K1RACT U]
470 Ohm [CR1206-JW-471ELF]	470 Ohm [PWR2615W4700JE]	470 Ohm [PWR6327W4700JE]	470 pF [C0603C471K2RACT U]
470 Ohm [CR1206-JW-471GLF]			
470 Ohm [CR2512-JW-471ELF]			

Multisim 14.1 Education Components

470 pF [C0603C471K3GACT U]	470 pF [C0805C471K2RACT U]	470 pF [C1210C471K5GACT U]	470 pF [CA064C471K8RAC]
470 pF [C0603C471K3HACT U]	470 pF [C0805C471K3RACT U]	470 pF [C1210C471KBGAC TU]	470 pF [GPC7.3471K63K31 TR12]
470 pF [C0603C471K3RACT U]	470 pF [C0805C471K4RACT U]	470 pF [C1210C471KCGAC TU]	470 pF [GPC7.3472K630K3 5TR12]
470 pF [C0603C471K4RACT U]	470 pF [C0805C471K5GACT U]	470 pF [C1812C471K5GACT U]	470 pF [SPC7.3471K100K31 TR12]
470 pF [C0603C471K5GACT U]	470 pF [C0805C471K5RACT U]	470 pF [C1812C471KBGAC TU]	470 pF [SPC7.3471K250K31 TR12]
470 pF [C0603C471K5HACT U]	470 pF [C0805C471KARACT U]	470 pF [C1825C471KBGAC TU]	470 pF [SPC7.3471K400K31 TR12]
470 pF [C0603C471K5RACT U]	470 pF [C1206C471K1GACT U]	470 pF [C2220C471KBGAC TU]	470 pF [SPC7.3471K630K31 TR12]
470 pF [C0603C471K8RACT U]	470 pF [C1206C471K2GACT U]	470 pF [C2225C471KBGAC TU]	470 pF [W2F11A4718AT1A]
470 pF [C0805C471K1GACT U]	470 pF [C1206C471K5GACT U]	470 pF [CA064C471K4RACT U]	470 uF [16SEPC470M]
470 pF [C0805C471K1RACT U]	470 pF [C1206C471KBGAC TU]	470 pF [CA064C471K5GAC TU]	470 uF [16SVPE470M]
470 pF [C0805C471K2GACT U]	470 pF [C1206C471KCGAC TU]	470 pF [CA064C471K5RACT U]	470 uF [2R5TPE470M7]
			470 uF [2R5TPE470M9]
			470 uF [2R5TPE470MC]

Multisim 14.1 Education Components

470 uF [2R5TPE470MF]	470 uF [6TPE470MI]	470 uF [EEFHX0D471R9]	470 uF [ETPF470M5H]
470 uF [2R5TPE470MI]	470 uF [6TPF470MAH]	470 uF [EEFHX0E471R]	470 uF [T489X477M006AT E200]
470 uF [2R5TPF470M6L]	470 uF [A700X477M002AT E007]	470 uF [EEFHX0E471R4]	470 uF [T491D477M004AT]
470 uF [2R5TPF470M7L]	470 uF [A700X477M002AT E010]	470 uF [EEFHX0E471R6]	470 uF [T491D477M006AT]
470 uF [2R5TPF470ML]	470 uF [A700X477M002AT E015]	470 uF [EEFHX0E471R9]	470 uF [T491D477M006AT]
470 uF [2TPE470MAJGB]	470 uF [A700X477M002AT E015]	470 uF [EEFLX0D471R]	470 uF [T491E477M006AT]
470 uF [4TPE470MCL]	470 uF [EEFCX0D471R]	470 uF [EEFLX0D471R4]	470 uF [T491E477M010AT]
470 uF [4TPE470MFL]	470 uF [EEFCX0E471R]	470 uF [EEFLX0E471R]	470 uF [T491X477M004AT]
470 uF [4TPE470MIL]	470 uF [EEFGX0D471L]	470 uF [EEFLX0E471R4]	470 uF [T491X477M006AT]
470 uF [4TPE470ML]	470 uF [EEFGX0D471R]	470 uF [EEFSX0D471E4]	470 uF [T491X477M010AT]
470 uF [4TPF470ML]	470 uF [EEFGX0E471L]	470 uF [EEFSX0D471ER]	470 uF [T494D477M004AT]
470 uF [6SEPC470MW]	470 uF [EEFGX0E471R]	470 uF [EEFSX0D471XE]	470 uF [T494D477M006AT]
470 uF [6SEPC470MX]	470 uF [EEFHX0D471R]	470 uF [EEFSX0E471E4]	470 uF [T494E477M006AT]
470 uF [6TPB470M]	470 uF [EEFHX0D471R4]	470 uF [EEFSX0E471ER]	470 uF [T494E477M006AT]
470 uF [6TPE470M]	470 uF [EEFHX0D471R6]	470 uF [EEFSX0E471XE]	470 uF [T494E477M010AT]
470 uF [6TPE470MAZU]			

Multisim 14.1 Education Components

470 uF [T494X477M004AT]	470 uF [T495X477M006AT E050]	470 uF [T520D477M004AT E010]	470 uF [T520V477M002AT E040]
470 uF [T494X477M006AT]	470 uF [T495X477M006AT E065]	470 uF [T520D477M004AT E012]	470 uF [T520V477M2R5AT E007]
470 uF [T494X477M010AT]	470 uF [T495X477M010AT E045]	470 uF [T520D477M004AT E015]	470 uF [T520V477M2R5AT E009]
470 uF [T495D477M006AT E100]	470 uF [T495X477M010AT E050]	470 uF [T520D477M004AT E018]	470 uF [T520V477M2R5AT E012]
470 uF [T495D477M006AT E125]	470 uF [T495X477M010AT E060]	470 uF [T520D477M004AT E025]	470 uF [T520V477M2R5AT E015]
470 uF [T495E477M006AT E040]	470 uF [T495X477M010AT E100]	470 uF [T520D477M004AT E040]	470 uF [T520V477M2R5AT E018]
470 uF [T495X477M004AT E030]	470 uF [T495X477M010AT E200]	470 uF [T520D477M006AT E025]	470 uF [T520W477M006AT E055]
470 uF [T495X477M004AT E045]	470 uF [T510X477M006AT E030]	470 uF [T520D477M006AT E030]	470 uF [T520X477M006AT E010]
470 uF [T495X477M004AT E100]	470 uF [T513X477M006AH 6110]	470 uF [T520D477M2R5AT E006]	470 uF [T520X477M006AT E018]
470 uF [T495X477M006AT E030]	470 uF [T520C477M2R5AT E025]	470 uF [T520D477M2R5AT E007]	470 uF [T520X477M006AT E035]
470 uF [T495X477M006AT E045]	470 uF [T520C477M2R5AT E045]	470 uF [T520D477M2R5AT E009]	470 uF [T520X477M006AT E040]

Multisim 14.1 Education Components

470 uF [T520Y477M006AT E010]	470 uF [T528Z477M2R5AT E012]	470 uF [TAJC477K002RNJ]	470 uF [TPME477K010R00 30]
470 uF [T520Y477M006AT E015]	470 uF [T530D477M004AT E006]	470 uF [TAJC477K004RNJ]	470 uF [TPSD477K004R004 5]
470 uF [T520Y477M006AT E018]	470 uF [T530D477M004AT E010]	470 uF [TAJD477K006RNJ]	470 uF [TPSD477K004R010 0]
470 uF [T520Y477M006AT E025]	470 uF [T530D477M2R5AT E006]	470 uF [TAJE477K004RNJ]	470 uF [TPSD477K006R010 0]
470 uF [T522Y477M006AT E040]	470 uF [T530X477M006AT E004]	470 uF [TAJE477K006RNJ]	470 uF [TPSD477K006R020 0]
470 uF [T525D477M003AT E025]	470 uF [T530X477M006AT E005]	470 uF [TAJV477K006RNJ]	470 uF [TPSE477K004R003 5]
470 uF [T525D477M004AT E025]	470 uF [T530X477M006AT E006]	470 uF [TAJV477K010RNJ]	470 uF [TPSE477K004R004 5]
470 uF [T525D477M004AT E040]	470 uF [T530X477M006AT E010]	470 uF [TAJY477K004RNJ]	470 uF [TPSE477K004R010 0]
470 uF [T525D477M2R5AT E025]	470 uF [T530Y477M004AT E005]	470 uF [TPME477K006R00 18]	470 uF [TPSE477K006R004 5]
470 uF [T528Z477M2R5AT E005]	470 uF [T530Y477M006AT E005]	470 uF [TPME477K006R00 23]	470 uF [TPSE477K006R005 0]
470 uF [T528Z477M2R5AT E009]	470 uF [T543D477M2R5AT E007]	470 uF [TPME477K010R00 23]	470 uF [TPSE477K006R006 0]

Multisim 14.1 Education Components

470 uF [TPSE477K006R010 0]	470 uF [TPSV477K010R006 0]	470 uH [SDR0906- 471KL]	470 uH [SRR0735A- 471M]
470 uF [TPSE477K006R020 0]	470 uF [TPSV477K010R010 0]	470 uH [SDR1005- 471KL]	470 uH [SRR0745A- 471M]
470 uF [TPSE477K010R004 5]	470 uF [TRJE477K006RRJ]	470 uH [SDR1006- 471KL]	470 uH [SRR0804- 471K]
470 uF [TPSE477K010R005 0]	470 uF [TRMD477K004R00 35]	470 uH [SDR1030- 471K]	470 uH [SRR0805- 471K]
470 uF [TPSE477K010R006 0]	470 uF [TRME477K006R00 30]	470 uH [SDR1045- 471K]	470 uH [SRR0905- 471K]
470 uF [TPSE477K010R010 0]	470 uH [SDE0805A- 471K]	470 uH [SDR1305- 471K]	470 uH [SRR0906- 471YL]
470 uF [TPSE477K010R020 0]	470 uH [SDE1006A- 471K]	470 uH [SDR1307- 471KL]	470 uH [SRR0908- 471YL]
470 uF [TPSE477K010R020 0]	470 uH [SDR0302- 471KL]	470 uH [SDR1307A-471K]	470 uH [SRR1003- 471Y]
470 uF [TPSV477K006R004 0]	470 uH [SDR0403- 471KL]	470 uH [SDR1806- 471KL]	470 uH [SRR1005- 471K]
470 uF [TPSV477K006R005 5]	470 uH [SDR0503- 471KL]	470 uH [SDR6603- 471M]	470 uH [SRR1205- 471KL]
470 uF [TPSV477K006R010 0]	470 uH [SDR0603- 471KL]	470 uH [SDR7030- 471K]	470 uH [SRR1206- 471KL]
470 uF [TPSV477K010R004 0]	470 uH [SDR0604- 471KL]	470 uH [SDR7045- 471K]	470 uH [SRR1208- 471KL]
470 uF [TPSV477K010R004 0]	470 uH [SDR0703- 471KL]	470 uH [SRN1060- 471M]	470 uH [SRR1210- 471M]
	470 uH [SDR0805- 471KL]	470 uH [SRR0603- 471KL]	470 uH [SRR1210A- 471M]
		470 uH [SRR0604- 471KL]	470 uH [SRR1240- 471K]

Multisim 14.1 Education Components

470 uH [SRR1260-471K]	475 kOhm [CR1206-FX-4753ELF]	48.7 kOhm [CR1206-FX-4872ELF]	4814P-3-331/471
470 uH [SRR1260A-471K]	475 Ohm [CAT16-4750F4LF]	48.7 kOhm [CRT1206-BY-4872ELF]	4814P-3-331/471LF
470 uH [SRR1280-471K]	475 Ohm [CAY16-4750F4LF]		4814P-3-501/501
470 uH [SRR1806-471M]	475 Ohm [CR0402-FX-4750GLF]		4814P-3-800/211
470 uH [SRR4028-471Y]	475 Ohm [CR0603-FX-4750ELF]	48.7 kOhm [CRT1206-FZ-4872ELF]	4814P-3-800/211LF
470 uH [SRR5028-471Y]	475 Ohm [CR0805-FX-4750ELF]	48.7 Ohm [CR0402-FX-48R7GLF]	4814P-T03-111/221
470 uH [SRR6028-471Y]	475 Ohm [CR1206-FX-4750ELF]	48.7 Ohm [CR0603-FX-48R7ELF]	4814P-T03-221/331
470 uH [SRR6603-471ML]	475 Ohm [CRM1206-FX-4750ELF]	48.7 Ohm [CR0805-FX-48R7ELF]	4814P-T03-262/362
470 uH [SRR7032-471M]	475 Ohm [CRT0603-BY-4750ELF]		4814P-T03-331/391
470 uH [SRR7045-471M]	48.7 kOhm [CR0201-FW-4872GLF]		4814P-T03-331/471
47151-0001	48.7 kOhm [CR0402-FX-4753GLF]	4814P-3-102/102LF	4814P-T03-501/501
47272-0001	48.7 kOhm [CR0402-FX-4872GLF]	48.7 Ohm [CR1206-FX-48R7ELF]	4816P-3-101/101
475 kOhm [CR0402-FX-4753GLF]	48.7 kOhm [CR0603-FX-4753ELF]	48.7 Ohm [CRT1206-FZ-48R7ELF]	4816P-3-101/101LF
475 kOhm [CR0603-FX-4753ELF]	48.7 kOhm [CR0805-FX-4753ELF]		4816P-3-102/332
475 kOhm [CR0805-FX-4753ELF]	48.7 kOhm [CR0805-FX-4872ELF]	4814P-3-102/102LF	4816P-3-121/471
			4816P-3-161/241
			4816P-3-181/271
			4816P-3-181/391
			4816P-3-181/391LF
			4816P-3-221/182
			4816P-3-221/221
			4816P-3-221/331
			4816P-3-221/331LF
			4816P-3-222/222
			4816P-3-222/562

Multisim 14.1 Education Components

4816P-3-271/471	4816P-T03-221/221	4820P-3-221/331	487 kOhm [CR1206-FX- 4873ELF]
4816P-3-302/622	4816P-T03-221/271	4820P-3-225/225	
4816P-3-302/622LF	4816P-T03- 221/271L	4820P-3-271/471	487 kOhm [CRT1206-FZ- 4873ELF]
4816P-3-331/331	4816P-T03-221/331	4820P-3-331/331LF	
4816P-3-331/391	4816P-T03- 221/331L	4820P-3-331/471	487 Ohm [CR0402- FX-4870GLF]
4816P-3-331/391LF	4816P-T03-222/562	4820P-3-331/471LF	
4816P-3-331/470	4816P-T03-271/471	4820P-3-331/680	487 Ohm [CR0603- FX-4870ELF]
4816P-3-331/471	4816P-T03-302/622	4820P-3-331/681	
4816P-3-331/471LF	4816P-T03-302/622L	4820P-3-332/332LF	487 Ohm [CR0805- FX-4870ELF]
4816P-3-391/391	4816P-T03-331/331	4820P-3-471/681	487 Ohm [CR1206- FX-4870ELF]
4816P-3-471/681	4816P-T03-331/391	4820P-T03-104/273	
4816P-3-681/102	4816P-T03-331/391L	4820P-T03-152/332	487 Ohm [CRT1206-FZ- 4870ELF]
4816P-3-800/211	4816P-T03-331/471	4820P-T03-181/391	
4816P-T03- 102/102F	4816P-T03-331/471L	4820P-T03-221/331	49 mOhm [PWR4412- 2SCR0490F]
4816P-T03-102/202	4816P-T03-331/471L	4820P-T03-271/471	
4816P-T03-102/332	4816P-T03-332/472	4820P-T03-331/471	49.9 kOhm [CAT16- 4992F4LF]
4816P-T03-121/121	4816P-T03-681/102	4820P-T03-331/681	
4816P-T03-121/471	4816P-T03-820/131	487 kOhm [CR0402-FX- 4873GLF]	49.9 kOhm [CAY16- 4992F4LF]
4816P-T03-122/562	4818P-T03-221/182	487 kOhm [CR0603-FX- 4873ELF]	49.9 kOhm [CR0402-FX- 4992GLF]
4816P-T03-151/151	4818P-T03-221/331	487 kOhm [CR0805-FX- 4873ELF]	49.9 kOhm [CR0603-FX- 4992ELF]
4816P-T03-161/241	4820P-3-104/273		
4816P-T03-181/301	4820P-3-152/332		
4816P-T03-181/391			
4816P-T03- 181/391L			

Multisim 14.1 Education Components

49.9 kOhm [CR1206-FX- 4992ELF]	49.9 Ohm [CR0603- FX-49R9GLF]	499 kOhm [CHV1206-FX- 4993ELF]	499 Ohm [CAT16- 4990F4LF]
49.9 kOhm [CRM2512-FX- 4992ELF]	49.9 Ohm [CR0805- FX-49R9ELF]	499 kOhm [CHV2512-FX- 4993ELF]	499 Ohm [CAY16- 4990F4LF]
49.9 kOhm [CRT0402-BY- 4992GLF]	49.9 Ohm [CR0805- FX-49R9GLF]	499 kOhm [CR0402-FX- 4993GLF]	499 Ohm [CR0402- FX-4990GLF]
49.9 kOhm [CRT0603-BY- 4992ELF]	49.9 Ohm [CR1206- FX-49R9ELF]	499 kOhm [CR0402-FX- 4993GLF]	499 Ohm [CR0603- FX-4990ELF]
49.9 kOhm [CRT0805-BY- 4992ELF]	49.9 Ohm [CR2512- FX-49R9ELF]	499 kOhm [CR0603-FX- 4993ELF]	499 Ohm [CR0805- FX-4990ELF]
49.9 kOhm [CRT0805-DZ- 4992ELF]	49.9 Ohm [CRM1206-FX- 49R9ELF]	499 kOhm [CR0805-FX- 4993ELF]	499 Ohm [CR1206- FX-4990ELF]
49.9 Ohm [CAT16- 49R9F4GLF]	49.9 Ohm [CRM2010-FX- 49R9ELF]	499 kOhm [CR1206-FX- 4993ELF]	499 Ohm [CR2512- FX-4990ELF]
49.9 Ohm [CAT16- 49R9F4LF]	49.9 Ohm [CRM2512-FX- 49R9ELF]	499 kOhm [CR1206-FX- 4993ELF]	499 Ohm [CRM1206-FX- 4990ELF]
49.9 Ohm [CAT16- 49R9F8LF]	49.9 Ohm [CRT0402-FZ- 49R9GLF]	499 kOhm [CRM1206-FX- 4993ELF]	499 Ohm [CRM2512-FX- 4990ELF]
49.9 Ohm [CAY16- 49R9F4LF]	49.9 Ohm [CRT0805-FV- 49R9ELF]	499 kOhm [CRM2512-FX- 4993ELF]	499 Ohm [CRT0402-BV- 4990GLF]
49.9 Ohm [CR0201- FW-49R9GLF]	49.9 Ohm [CRT0805-FV- 49R9ELF]	499 kOhm [CRT0603-BY- 4993ELF]	499 Ohm [CRT0402-BY- 4990GLF]
49.9 Ohm [CR0402- FX-49R9GLF]	49.9 Ohm [CRT1206-BY- 49R9ELF]	499 kOhm [CRT0603-BY- 4993ELF]	499 Ohm [CRT0805-DZ- 4993ELF]
49.9 Ohm [CR0603- FX-49R9ELF]	49.9 Ohm [CRT1206-DY- 49R9ELF]	499 kOhm [CRT0805-DZ- 4993ELF]	499 Ohm [CRT1206-DY- 4990ELF]
	499 kOhm [CAY16- 4993F4LF]	499 kOhm [CRT1206-BY- 4993ELF]	499 Ohm [PWR5322W4990FE]

Multisim 14.1 Education Components

4Line_Bussed	5 kOhm [4308H-102-502]	5 mH [SDR0503-502JL]	5 Ohm [PWR163S-25-5R00F]
4Line_Isolated			
4Line_Terminator	5 kOhm [4308R-101-502]	5 mOhm [CRE2512-FZ-R005E-2]	5 Ohm [PWR163S-25-5R00FE]
4P1S	5 kOhm [4310R-101-502]	5 mOhm [CRE2512-FZ-R005E-3]	5 Ohm [PWR163S-25-5R00J]
4P2S			
4P3S	5 kOhm [4310R-101-502LF]	5 mOhm [CRF0805-FX-R005ELF]	5 Ohm [PWR163S-25-5R00JE]
4P4S	5 kOhm [4605X-101-502LF]	5 mOhm [CRF2512-FX-R005ELF]	5 Ohm [PWR2010W5R00JE]
4P5S			
4POS_ROTARY	5 kOhm [4605X-AP1-502LF]	5 mOhm [CRF2512-JX-R005ELF]	5 Ohm [PWR220T-20-5R00J]
4V_0.5W			
5 kOhm [4108R-1-502LF]	5 kOhm [4608X-102-502LF]	5 mOhm [PWR4412-2SBR0050F]	5 Ohm [PWR220T-35-5R00F]
5 kOhm [4114R-1-502]	5 kOhm [4608X-AP1-502LF]	5 mOhm [PWR4412-2SBR0050J]	5 Ohm [PWR220T-35-5R00J]
5 kOhm [4114R-1-502LF]	5 kOhm [4610H-101-502LF]		5 Ohm [PWR221T-30-5R00F]
5 kOhm [4114R-2-502]	5 kOhm [4610X-101-502LF]	5 mOhm [PWR4412-2SCR0050F]	5 Ohm [PWR221T-30-5R00J]
5 kOhm [4116R-1-502]	5 kOhm [4816P-1-502]	5 mOhm [PWR4412-2SDR0050F]	5 Ohm [PWR221T-50-5R00J]
5 kOhm [4116R-1-502LF]	5 kOhm [4816P-2-502]	5 mOhm [PWR4412-2SDR0050J]	5 Ohm [PWR263S-20-5R00F]
5 kOhm [4116R-2-502]	5 kOhm [4816P-2-502LF]		5 Ohm [PWR263S-35-5R00F]
5 kOhm [4116R-2-502LF]	5 kOhm [PWR221T-30-5001F]	5 mOhm [PWR6327WR005J]	5 Ohm [PWR263S-35-5R00J]
5 kOhm [4306R-101-502]	5 kOhm [PWR263S-35-5001F]	5 mOhm [PWR6327WR005JE]	5 Ohm [PWR263S-35-5R00JE]

Multisim 14.1 Education Components

5 Ohm [PWR3014W5R00JE]	5 uH [SRU1038A- 5R0Y]	5.1 kOhm [4308M- 102-512]	5.1 kOhm [4605X- 101-512LF]
5 Ohm [PWR4318W5R00JE]	5.1 kOhm [4114R- 1-512]	5.1 kOhm [4308M- 102-512LF]	5.1 kOhm [4605X- AP1-512LF]
5 Ohm [PWR4525W5R00J]	5.1 kOhm [4114R- 1-512LF]	5.1 kOhm [4308R- 101-512]	5.1 kOhm [4606X- 101-512LF]
5 Ohm [PWR5322W5R00JE]	5.1 kOhm [4114R- 2-512]	5.1 kOhm [4308R- 101-512LF]	5.1 kOhm [4606X- 102-512LF]
5 Ohm [PWR5322W5R00JE]	5.1 kOhm [4116R- 1-512]	5.1 kOhm [4308R- 102-512]	5.1 kOhm [4607X- 101-512LF]
5 Ohm [PWR6327W5R00J]	5.1 kOhm [4116R- 1-512LF]	5.1 kOhm [4308R- 102-512LF]	5.1 kOhm [4608X- 101-512LF]
5 uH [SDR0603- 5R0ML]	5.1 kOhm [4116R- 2-512]	5.1 kOhm [4310H- 101-512]	5.1 kOhm [4608X- 102-512LF]
5 uH [SRR0804- 5R0M]	5.1 kOhm [4116R- 2-512LF]	5.1 kOhm [4310H- 101-512LF]	5.1 kOhm [4608X- AP1-512LF]
5 uH [SRR1205- 5R0ML]	5.1 kOhm [4306M- 101-512]	5.1 kOhm [4310M- 101-512]	5.1 kOhm [4609X- 101-512LF]
5 uH [SRR1206- 5R0ML]	5.1 kOhm [4306M- 101-512LF]	5.1 kOhm [4310M- 101-512LF]	5.1 kOhm [4610X- 101-512LF]
5 uH [SRR5018- 5R0Y]	5.1 kOhm [4306M- 102-512]	5.1 kOhm [4310M- 102-512]	5.1 kOhm [4610X- 102-512LF]
5 uH [SRR6028- 5R0Y]	5.1 kOhm [4306M- 102-512LF]	5.1 kOhm [4310M- 102-512LF]	5.1 kOhm [4814P- 1-512]
5 uH [SRR6038- 5R0Y]	5.1 kOhm [4306R- 101-512LF]	5.1 kOhm [4310R- 101-512]	5.1 kOhm [4814P- 1-512LF]
5 uH [SRR6040A- 5R0Y]	5.1 kOhm [4308M- 101-512]	5.1 kOhm [4310R- 101-512LF]	5.1 kOhm [4814P- 2-512]
5 uH [SRU1038- 5R0Y]	5.1 kOhm [4308M- 101-512LF]	5.1 kOhm [4416P- 1-512]	5.1 kOhm [4814P- 2-512LF]

Multisim 14.1 Education Components

5.1 kOhm [4816P-1-512]	5.1 kOhm [CAY10-512J4LF]	5.1 kOhm [CRM2512-FX-5101ELF]	5.1 MOhm [CR0805-JW-515ELF]
5.1 kOhm [4816P-1-512F]	5.1 kOhm [CAY16-512J4LF]	5.1 kOhm [CRT0603-BY-5101ELF]	5.1 MOhm [CR1206-JW-515ELF]
5.1 kOhm [4816P-1-512LF]	5.1 kOhm [CAY17-512JALF]	5.1 kOhm [CRT0603-FX-5101ELF]	5.1 nF [C0603C512K3HACTU]
5.1 kOhm [4816P-2-512]	5.1 kOhm [CR0402-FX-5101GLF]	5.1 kOhm [CRT0603-FY-5101ELF]	5.1 nF [C0603C512K5HACTU]
5.1 kOhm [4816P-2-512LF]	5.1 kOhm [CR0402-JW-512GLF]	5.1 kOhm [CRT0805-BW-5101ELF]	5.1 nF [C0805C512K1GACTU]
5.1 kOhm [4816P-T01-512]	5.1 kOhm [CR0603-FX-5101ELF]	5.1 kOhm [CRT0805-FX-5101ELF]	5.1 nF [C0805C512K1HACTU]
5.1 kOhm [4816P-T01-512LF]	5.1 kOhm [CR0805-FX-5101GLF]	5.1 kOhm [CRT1206-BY-5101ELF]	5.1 nF [C0805C512K3HACTU]
5.1 kOhm [4816P-T02-512]	5.1 kOhm [CR0805-FX-5101GLF]	5.1 MOhm [4604X-102-515LF]	5.1 nF [C0805C512K5HACTU]
5.1 kOhm [4816P-T02-512LF]	5.1 kOhm [CR1206-FX-5101ELF]	5.1 MOhm [CHV0603-FX-5104ELF]	5.1 nF [C1206C512K5GACTU]
5.1 kOhm [4820P-1-512F]	5.1 kOhm [CR1206-JW-512ELF]	5.1 MOhm [CR0402-JW-515GLF]	5.1 nF [C2220C512KBGACTU]
5.1 kOhm [4820P-2-512]	5.1 kOhm [CR2010-JW-512ELF]	5.1 MOhm [CR0603-JW-515ELF]	5.1 nF [C2225C512KBGACTU]
5.1 kOhm [CAT10-512J4LF]	5.1 kOhm [CR2512-JW-512ELF]		
5.1 kOhm [CAT16-512J4LF]	5.1 kOhm [CRM1206-JW-512ELF]		
5.1 kOhm [CAT16-512J8LF]			
5.1 kOhm [CAT25-512JALF]			

Multisim 14.1 Education Components

5.1 Ohm [CAT10-5R1J4LF]	5.1 Ohm [CRL0603-JW-5R10ELF]	5.1 Ohm [PWR5322W5R10JE]	5.11 MOhm [CR1206-FW-5114ELF]
5.1 Ohm [CAT16-5R1J2LF]	5.1 Ohm [CRL0805-FW-5R10ELF]	5.11 kOhm [CAY16-5111F4LF]	5.11 Ohm [CRM1206-FX-5R11ELF]
5.1 Ohm [CAT16-5R1J4GLF]	5.1 Ohm [CRL1206-FW-5R10ELF]	5.11 kOhm [CR0402-FX-5111GLF]	5.2 uH [SRU1038-5R2Y]
5.1 Ohm [CAT16-5R1J4LF]	5.1 Ohm [CRL2010-FW-5R10ELF]	5.11 kOhm [CR0603-FX-5111ELF]	5.23 kOhm [CR0402-FX-5231GLF]
5.1 Ohm [CAY10-5R1J2LF]	5.1 Ohm [CRL2010-JW-5R10ELF]	5.11 kOhm [CR0805-FX-5111ELF]	5.23 kOhm [CR0603-FX-5231ELF]
5.1 Ohm [CAY10-5R1J4LF]	5.1 Ohm [CRL2512-FW-5R10ELF]	5.11 kOhm [CR1206-FX-5111ELF]	5.23 kOhm [CR0805-FX-5231ELF]
5.1 Ohm [CR0402-J/-5R1GLF]	5.1 Ohm [CRM1206-JW-5R1ELF]	5.11 kOhm [CRT0402-BY-5111GLF]	5.23 kOhm [CR1206-FX-5231ELF]
5.1 Ohm [CR0603-J/-5R1ELF]	5.1 Ohm [CRM2512-FX-5R10ELF]	5.11 kOhm [CRT0402-FZ-5111GLF]	5.3 uH [SRR5028-5R3Y]
5.1 Ohm [CR0603-J/-5R1GLF]	5.1 Ohm [CRM2512-JW-5R1ELF]	5.11 kOhm [CRT0603-BY-5111ELF]	5.36 kOhm [CR0402-FX-5361GLF]
5.1 Ohm [CR0805-J/-5R1ELF]	5.1 Ohm [CRT0805-BW-5R10ELF]	5.11 kOhm [CRT0805-BW-5111ELF]	5.36 kOhm [CR0603-FX-5361ELF]
5.1 Ohm [CR1206-J/-5R1ELF]	5.1 Ohm [FW10A5R10JA]	5.11 kOhm [CRT0805-CX-5111ELF]	5.36 kOhm [CR0805-FX-5361ELF]
5.1 Ohm [CR1206-J/-5R1GLF]	5.1 Ohm [FW30A5R10JA]		
5.1 Ohm [CR2010-J/-5R1ELF]	5.1 Ohm [FW50A5R10JA]		
5.1 Ohm [CRL0603-FW-5R10ELF]	5.1 Ohm [PWR4318W5R10JE]		

Multisim 14.1 Education Components

5.36 kOhm [CR1206-FX- 5361ELF]	5.6 kOhm [4114R- 2-562]	5.6 kOhm [4306R- 102-562LF]	5.6 kOhm [4310R- 101-562]
5.36 kOhm [CRT0603-BY- 5361ELF]	5.6 kOhm [4114R- 2-562LF]	5.6 kOhm [4308H- 101-562]	5.6 kOhm [4310R- 101-562LF]
5.4 uH [SRR5018- 5R4Y]	5.6 kOhm [4116R- 1-562]	5.6 kOhm [4308H- 101-562LF]	5.6 kOhm [4310R- 102-562]
5.49 kOhm [CAY16- 5491F4LF]	5.6 kOhm [4116R- 2-562]	5.6 kOhm [4308H- 102-562LF]	5.6 kOhm [4310R- 102-562LF]
5.49 kOhm [CR0402-FX- 5491GLF]	5.6 kOhm [4116R- 2-562LF]	5.6 kOhm [4308M- 101-562]	5.6 kOhm [4416P- 2-562]
5.49 kOhm [CR0603-FX- 5491ELF]	5.6 kOhm [4116R- 2-562LF]	5.6 kOhm [4308M- 101-562LF]	5.6 kOhm [4416P- T01-562]
5.49 kOhm [CR0805-FX- 5491ELF]	5.6 kOhm [4304M- 102-562]	5.6 kOhm [4308M- 102-562]	5.6 kOhm [4416P- T02-562]
5.49 kOhm [CR0805-FX- 5491ELF]	5.6 kOhm [4304M- 102-562LF]	5.6 kOhm [4308M- 102-562LF]	5.6 kOhm [4420P- 2-562]
5.49 kOhm [CR1206-FX- 5491ELF]	5.6 kOhm [4306H- 102-562]	5.6 kOhm [4308R- 101-562]	5.6 kOhm [4420P- 2-562LF]
5.49 kOhm [CR1206-FX- 5491ELF]	5.6 kOhm [4306H- 102-562LF]	5.6 kOhm [4308R- 101-562LF]	5.6 kOhm [4420P- T02-562]
5.49 kOhm [CRT0603-CW- 5491ELF]	5.6 kOhm [4306M- 101-562]	5.6 kOhm [4308R- 102-562]	5.6 kOhm [4604X- 101-562LF]
5.49 kOhm [CRT0805-CX- 5491ELF]	5.6 kOhm [4306M- 101-562LF]	5.6 kOhm [4308R- 102-562LF]	5.6 kOhm [4604X- 102-562LF]
5.49 kOhm [CRT0805-CX- 5491ELF]	5.6 kOhm [4306R- 101-562]	5.6 kOhm [4309R- 101-562]	5.6 kOhm [4605H- 101-562FLF]
5.6 kOhm [4114R- 1-562]	5.6 kOhm [4306R- 101-562LF]	5.6 kOhm [4309R- 101-562LF]	5.6 kOhm [4605X- 101-562LF]
5.6 kOhm [4114R- 1-562LF]	5.6 kOhm [4306R- 102-562]	5.6 kOhm [4310M- 101-562]	5.6 kOhm [4606H- 101-562LF]

Multisim 14.1 Education Components

5.6 kOhm [4606X-101-562LF]	5.6 kOhm [4814P-1-562]	5.6 kOhm [CAT10-562J4LF]	5.6 kOhm [CR0603-JW-562GLF]
5.6 kOhm [4606X-102-562LF]	5.6 kOhm [4814P-2-562]	5.6 kOhm [CAT16-5601F4LF]	5.6 kOhm [CR0805-FX-5601ELF]
5.6 kOhm [4606X-AP1-562LF]	5.6 kOhm [4814P-T01-562]	5.6 kOhm [CAT16-5601F8LF]	5.6 kOhm [CR0805-JW-562ELF]
5.6 kOhm [4606X-AP2-562LF]	5.6 kOhm [4814P-T01-562LF]	5.6 kOhm [CAT16-562J4LF]	5.6 kOhm [CR1206-FX-5601ELF]
5.6 kOhm [4607X-101-562LF]	5.6 kOhm [4814P-T02-562]	5.6 kOhm [CAT16-562J8LF]	5.6 kOhm [CR1206-JW-562ELF]
5.6 kOhm [4608X-101-562LF]	5.6 kOhm [4814P-T02-562LF]	5.6 kOhm [CAT25-562JALF]	5.6 kOhm [CR2010-JW-562ELF]
5.6 kOhm [4608X-102-562LF]	5.6 kOhm [4816P-1-562]	5.6 kOhm [CAY10-562J4LF]	5.6 kOhm [CR2512-JW-562ELF]
5.6 kOhm [4608X-AP2-562LF]	5.6 kOhm [4816P-1-562LF]	5.6 kOhm [CAY16-5601F4LF]	5.6 kOhm [CRM2512-JW-562ELF]
5.6 kOhm [4609H-101-562LF]	5.6 kOhm [4816P-2-562]	5.6 kOhm [CAY16-562J4LF]	5.6 kOhm [CRT0805-PV-5601ELF]
5.6 kOhm [4609M-101-562LF]	5.6 kOhm [4816P-2-562LF]	5.6 kOhm [CAY16-562J8LF]	5.6 kOhm [PWR263S-35-5601FE]
5.6 kOhm [4609X-101-562LF]	5.6 kOhm [4816P-T01-562]	5.6 kOhm [CAY17-562JALF]	5.6 kOhm [PWR4525W5601J]
5.6 kOhm [4610X-101-562LF]	5.6 kOhm [4816P-T01-562LF]	5.6 kOhm [CR0402-FX-5601GLF]	5.6 mH [SDR0503-562JL]
5.6 kOhm [4610X-102-562LF]	5.6 kOhm [4816P-T02-562]	5.6 kOhm [CR0402-JW-562GLF]	5.6 mH [SDR0906-562KL]
5.6 kOhm [4610X-AP1-562LF]	5.6 kOhm [4816P-T02-562LF]	5.6 kOhm [CR0603-FX-5601ELF]	5.6 mH [SRR0906-562YL]
5.6 kOhm [4612X-102-562LF]	5.6 kOhm [4820P-T02-562]	5.6 kOhm [CR0603-JW-562ELF]	

Multisim 14.1 Education Components

5.6 mH [SRR1208-562KL]	5.6 nF [C0603C562K1RACTU]	5.6 nF [C0805C562K2RACTU]	5.6 nF [C1206C562K5RACTU]
5.6 MOhm [4608X-102-565LF]	5.6 nF [C0603C562K3GACTU]	5.6 nF [C0805C562K3GACTU]	5.6 nF [C1206C562KARACTU]
5.6 MOhm [4610X-102-565LF]	5.6 nF [C0603C562K3HACTU]	5.6 nF [C0805C562K3HACTU]	5.6 nF [C1210C562K5GACTU]
5.6 MOhm [CR0402-JW-565GLF]	5.6 nF [C0603C562K3RACTU]	5.6 nF [C0805C562K3RACTU]	5.6 nF [C1210C562K5RACTU]
5.6 MOhm [CR0603-JW-565ELF]	5.6 nF [C0603C562K4RACTU]	5.6 nF [C0805C562K4RACTU]	5.6 nF [C1210C562KARACTU]
5.6 MOhm [CR0805-JW-565ELF]	5.6 nF [C0603C562K5HACTU]	5.6 nF [C0805C562K5HACTU]	5.6 nF [C1812C562K2GACTU]
5.6 MOhm [CR1206-JW-565ELF]	5.6 nF [C0603C562K5RACTU]	5.6 nF [C0805C562K5RACTU]	5.6 nF [C2220C562KBGAC TU]
5.6 MOhm [CR2512-JW-565ELF]	5.6 nF [C0603C562K8RACTU]	5.6 nF [C0805C562KARACTU]	5.6 nF [C2225C562KBGAC TU]
5.6 nF [C0402C562K3RACTU]	5.6 nF [C0805C562K1GACTU]	5.6 nF [C1206C562K1RACTU]	5.6 nF [GMC5.7562K100J3 1TR12]
5.6 nF [C0402C562K4RACTU]	5.6 nF [C0805C562K1HACTU]	5.6 nF [C1206C562K2RACTU]	5.6 nF [GMC5.7562K250J3 1TR12]
5.6 nF [C0402C562K5RACTU]	5.6 nF [C0805C562K1RACTU]	5.6 nF [C1206C562K5GACTU]	5.6 nF [GMC5.7562K50J31 TR12]

Multisim 14.1 Education Components

5.6 nF [GMC7.3562K100K3 1TR12]	5.6 nF [MMC7.3562K63K3 1TR12]	5.6 Ohm [CRM2512-JW- 5R6ELF]	5.6 Ohm [PWR263S-35- 5R60F]
5.6 nF [GMC7.3562K400K3 1TR12]	5.6 Ohm [CR0402- J/-5R6GLF]	5.6 Ohm [CRT0805- BW-5R60ELF]	5.6 Ohm [PWR263S-35- 5R60FE]
5.6 nF [GMC7.3562K63K31 TR12]	5.6 Ohm [CR0603- J/-5R6ELF]	5.6 Ohm [CRT0805- FZ-5R60ELF]	5.6 Ohm [PWR263S-35- 5R60J]
5.6 nF [GMC7.3563K100K3 3TR12]	5.6 Ohm [CR1206- J/-5R6ELF]	5.6 Ohm [FW20A5R60JA]	5.6 uF [25TQC5R6M]
5.6 nF [MMC5.7562K100J 31TR12]	5.6 Ohm [CR2010- J/-5R6ELF]	5.6 Ohm [FW30A5R60JA]	5.6 uF [C0805C565K9PACT U]
5.6 nF [MMC5.7562K250J 31TR12]	5.6 Ohm [CRL0603- FW-5R60ELF]	5.6 Ohm [PWR163S-25- 5R60F]	5.6 uF [C1206C565K4RACT U]
5.6 nF [MMC5.7562K50J3 1TR12]	5.6 Ohm [CRL0805- FW-5R60ELF]	5.6 Ohm [PWR163S-25- 5R60J]	5.6 uF [C1206C565K8RACT U]
5.6 nF [MMC7.3562K100K 31TR12]	5.6 Ohm [CRL1206- FW-5R60ELF]	5.6 Ohm [PWR220T-20- 5R60F]	5.6 uF [C1206C565K9RACT U]
5.6 nF [MMC7.3562K250K 31TR12]	5.6 Ohm [CRL1206- JW-5R60ELF]	5.6 Ohm [PWR220T-20- 5R60J]	5.6 uF [C1210C565K4PACT U]
5.6 nF [MMC7.3562K400K 33TR12]	5.6 Ohm [CRL2010- FW-5R60ELF]	5.6 Ohm [PWR263S-20- 5R60F]	5.6 uF [MDC10565K100A5 5P4TUBE]
5.6 nF [MMC7.3562K50K3 1TR12]	5.6 Ohm [CRL2512- FW-5R60ELF]	5.6 Ohm [PWR263S-20- 5R60J]	5.6 uF [MDC10565K100A5 5P5TUBE]
	5.6 Ohm [CRM1206-FX- 5R60ELF]		

Multisim 14.1 Education Components

5.6 uF [MDC10565K50A54 P3TUBE]	5.6 uH [SDR0805- 5R6ML]	5.6 uH [SRP4020TA-5R6M]	5.6 uH [SRR1260A- 5R6Y]
5.6 uF [MDC10565K50A54 P4TUBE]	5.6 uH [SDR0906- 5R6ML]	5.6 uH [SRP5015TA-5R6M]	5.6 uH [SRR1280- 5R6Y]
5.6 uF [MDC15565K100B5 5P3TUBE]	5.6 uH [SDR1006- 5R6ML]	5.6 uH [SRP5030T- 5R6M]	5.6 uH [SRR4018- 5R6Y]
5.6 uF [MDC15565K100B5 5P4TUBE]	5.6 uH [SDR1307- 5R6ML]	5.6 uH [SRP5030TA-5R6M]	5.6 uH [SRR4028- 5R6Y]
5.6 uF [MDC15565K100B5 5P4TUBE]	5.6 uH [SDR1307A- 5R6M]	5.6 uH [SRP6540- 5R6M]	5.6 uH [SRR7045- 5R6M]
5.6 uF [MDC15565K50B53 P3TUBE]	5.6 uH [SDR1806- 5R6ML]	5.6 uH [SRP7028A- 5R6M]	5.62 kOhm [CAY16- 5621F4LF]
5.6 uF [MDS15565K50B53 P3TUBE]	5.6 uH [SRN5020- 5R6M]	5.6 uH [SRP7030- 5R6FM]	5.62 kOhm [CR0402-FX- 5621GLF]
5.6 uH [SDE0604A- 5R6M]	5.6 uH [SRP1040- 5R6M]	5.6 uH [SRP7050TA-5R6M]	5.62 kOhm [CR0603-FX- 5621ELF]
5.6 uH [SDE0805A- 5R6M]	5.6 uH [SRP1235- 5R6M]	5.6 uH [SRR0805- 5R6M]	5.62 kOhm [CR0805-FX- 5621ELF]
5.6 uH [SDE1006A- 5R6M]	5.6 uH [SRP1245A- 5R6M]	5.6 uH [SRR0906- 5R6ML]	5.62 kOhm [CR1206-FX- 5621ELF]
5.6 uH [SDR0302- 5R6ML]	5.6 uH [SRP1265A- 5R6M]	5.6 uH [SRR0908- 5R6ML]	5.62 kOhm [CR2010-FX- 5621ELF]
5.6 uH [SDR0403- 5R6ML]	5.6 uH [SRP1270- 5R6M]	5.6 uH [SRR1210- 5R6Y]	5.62 kOhm [CR2010-FX- 5621ELF]
5.6 uH [SDR0604- 5R6ML]	5.6 uH [SRP1770TA-5R6M]	5.6 uH [SRR1210A- 5R6Y]	5.62 kOhm [CRT0402-BY- 5621GLF]
5.6 uH [SDR0703- 5R6ML]	5.6 uH [SRP4012TA-5R6M]	5.6 uH [SRR1240- 5R6M]	5.62 kOhm [CRT0402-FZ- 5621GLF]
	5.6 uH [SRP4020- 5R6M]	5.6 uH [SRR1260- 5R6Y]	

Multisim 14.1 Education Components

5.62 kOhm [CRT0603-BY-5621ELF]	5.8 uH [SRP1205-5R6Y]	50 kOhm [PWR263S-35-5002F]	50 mOhm [CRM2010-FX-R050ELF]
5.62 kOhm [CRT0805-BY-5621ELF]	5.9 kOhm [CR0402-FX-5901GLF]	50 mOhm [CRA2512-FZ-R050ELF]	50 mOhm [CRM2512-FX-R050ELF]
5.62 kOhm [CRT1206-FZ-5621ELF]	5.9 kOhm [CR0603-FX-5901ELF]	50 mOhm [CRA2512-JZ-R050ELF]	50 mOhm [PWR163S-25-R050J]
5.62 Ohm [CRM1206-FX-5R62ELF]	5.9 kOhm [CR1206-FX-5901ELF]	50 mOhm [CRF2512-FZ-R050ELF]	50 mOhm [PWR163S-25-R050JE]
5.62 Ohm [CRT0805-BY-5R62ELF]	5 AMP	50 mOhm [CRL0805-FW-R050ELF]	50 mOhm [PWR1913WR050F]
5.76 kOhm [CR0402-FX-5761GLF]	50 kOhm [4108R-1-503]	50 mOhm [CRL0805-JW-R050ELF]	50 mOhm [PWR1913WR050J]
5.76 kOhm [CR0603-FX-5761ELF]	50 kOhm [4116R-1-503]	50 mOhm [CRL2010-FW-R050ELF]	50 mOhm [PWR1913WR050JE]
5.76 kOhm [CR0805-FX-5761ELF]	50 kOhm [4116R-2-503]	50 mOhm [CRL2512-FW-R050ELF]	50 mOhm [PWR220T-20-R050J]
5.76 kOhm [CR1206-FX-5761ELF]	50 kOhm [4116R-2-503LF]	50 mOhm [CRL2512-JW-R050ELF]	50 mOhm [PWR221T-30-R050J]
5.76 kOhm [CRT0603-BX-5761ELF]	50 kOhm [4604X-102-503LF]	50 mOhm [CRM0805-FW-R050ELF]	50 mOhm [PWR2615WR050F]
5.76 kOhm [CRT0603-BY-5761ELF]	50 kOhm [4820P-2-503]	50 mOhm [CRM1206-FX-R050ELF]	50 mOhm [PWR2615WR050F]
	50 kOhm [PWR221T-30-5002J]		

Multisim 14.1 Education Components

50 mOhm [PWR2615WR050J]	50 Ohm [4116R-1-500]	50 Ohm [4606X-102-500LF]	50 Ohm [PWR221T-30-50R0F]
50 mOhm [PWR2615WR050JE]	50 Ohm [4116R-1-500LF]	50 Ohm [4816P-T02-500]	50 Ohm [PWR221T-30-50R0J]
50 mOhm [PWR4412-2SBR0500F]	50 Ohm [4304M-102-500]	50 Ohm [4820P-1-500]	50 Ohm [PWR263S-20-50R0F]
50 mOhm [PWR4412-2SCR0500F]	50 Ohm [4306R-101-500]	50 Ohm [CAT25-500JALF]	50 Ohm [PWR263S-20-50R0J]
50 mOhm [PWR4412-2SDR0500F]	50 Ohm [4308R-101-500]	50 Ohm [PWR163S-25-50R0F]	50 Ohm [PWR263S-20-50R0JE]
50 mOhm [PWR4412-2SDR0500J]	50 Ohm [4308R-101-500LF]	50 Ohm [PWR163S-25-50R0FE]	50 Ohm [PWR263S-35-50R0F]
50 mOhm [PWR4412-2SDR0500J]	50 Ohm [4308R-102-500]	50 Ohm [PWR163S-25-50R0JE]	50 uH [SRR1205-500YL]
50 mOhm [PWR4525WR050J]	50 Ohm [4310R-101-500]	50 Ohm [PWR1913W50R0J]	50_AMP
50 mOhm [PWR4525WR050JE]	50 Ohm [4310R-101-500LF]	50 Ohm [PWR220T-20-50R0F]	500 mOhm [CRM2512-FX-R500ELF]
50 mOhm [PWR4525W-R050JE]	50 Ohm [4310R-102-500LF]	50 Ohm [PWR220T-20-50R0J]	500 mOhm [PWR163S-25-R500F]
50 mOhm [PWR6327WR050J]	50 Ohm [4420P-2-500]	50 Ohm [PWR220T-35-50R0J]	500 mOhm [PWR163S-25-R500FE]
50 mOhm [PWR6327WR050JE]	50 Ohm [4420P-T02-500]		

Multisim 14.1 Education Components

500 mOhm [PWR163S-25- R500J]	500 mOhm [PWR263S-20- R500J]	500 Ohm [4306R- 101-501]	51 kOhm [4116R-1- 513LF]
500 mOhm [PWR2010WR500F E]	500 mOhm [PWR263S-35- R500F]	500 Ohm [4306R- 101-501LF]	51 kOhm [4306R- 101-513]
500 mOhm [PWR2010WR500JE]	500 mOhm [PWR263S-35- R500J]	500 Ohm [4605X- 101-501LF]	51 kOhm [4308R- 102-513]
500 mOhm [PWR220T-20- R500F]	500 mOhm [PWR3014WR500JE]	500 Ohm [4816P-1- 501LF]	51 kOhm [4308R- 102-513LF]
500 mOhm [PWR220T-20- R500J]	500 mOhm [PWR4318WR500JE]	500 Ohm [4816P- T01-501]	51 kOhm [4310H- 101-513]
500 mOhm [PWR221T-30- R500F]	500 mOhm [PWR4525WR500J]	500 Ohm [4816P- T01-501LF]	51 kOhm [4310M- 101-513]
500 mOhm [PWR221T-30- R500J]	500 mOhm [PWR5322WR500JE]	500 Ohm [CAT16- 501J4LF]	51 kOhm [4310R- 101-513]
500 mOhm [PWR221T-50- R500F]	500 mOhm [PWR6327WR500F]	500 Ohm [PWR221T-30- 5000F]	51 kOhm [4310R- 101-513LF]
500 mOhm [PWR2615WR500F]	500 nH [SRN8040- R50Y]	500 Ohm [PWR263S-35- 5000J]	51 kOhm [4310R- 102-513]
500 mOhm [PWR2615WR500F E]	500 nH [SRP1040- R50M]	500 uOhm [CST0612-FC- R0005-E]	51 kOhm [4604X- 101-513LF]
500 mOhm [PWR263S-20- R500F]	500 nH [SRP1250- R50M]	50A02CH-TL-E	51 kOhm [4606X- 101-513LF]
	500 Ohm [4116R-1- 501]	50A02CH-TL-H	51 kOhm [4608X- 101-513LF]
	500 Ohm [4116R-1- 501LF]	50C02CH-TL-E	51 kOhm [4609X- 101-513LF]
		50C02MH-TL-E	51 kOhm [4610X- 101-513LF]
		50C02SS-TL-E	51 kOhm [4610X- 102-513LF]
		51 kOhm [4116R-1- 513]	

Multisim 14.1 Education Components

51 kOhm [4814P-2-513]	51 kOhm [CR0201-FW-5102GLF]	51 kOhm [CRT1206-BW-5102ELF]	51 Ohm [4306R-101-510]
51 kOhm [4814P-2-513LF]	51 kOhm [CR0402-FX-5102GLF]	51 mF [C0805C519K3GACTU]	51 Ohm [4306R-101-510LF]
51 kOhm [4814P-T02-513]	51 kOhm [CR0402-JW-513GLF]	51 mF [C0805C519KBGAC TU]	51 Ohm [4308H-102-510]
51 kOhm [4816P-1-513]	51 kOhm [CR0603-FX-5102ELF]	51 MOhm [CHV2010-JW-516ELF]	51 Ohm [4308R-102-510]
51 kOhm [4816P-1-513LF]	51 kOhm [CR0603-JW-513ELF]	51 mOhm [PWR4412-2SCR0510F]	51 Ohm [4308R-102-510LF]
51 kOhm [4816P-2-513]	51 kOhm [CR0805-FX-5102ELF]	51 Ohm [4114R-1-510]	51 Ohm [4310M-101-510]
51 kOhm [4816P-2-513LF]	51 kOhm [CR0805-JW-513ELF]	51 Ohm [4114R-1-510LF]	51 Ohm [4310M-101-510LF]
51 kOhm [4820P-2-513]	51 kOhm [CR1206-FX-5102ELF]	51 Ohm [4116R-1-510]	51 Ohm [4310R-101-510]
51 kOhm [4820P-T02-513]	51 kOhm [CR1206-JW-513ELF]	51 Ohm [4116R-1-510LF]	51 Ohm [4310R-102-510]
51 kOhm [CAT16-513J4LF]	51 kOhm [CR2010-JW-513ELF]	51 Ohm [4116R-2-510]	51 Ohm [4310R-102-510LF]
51 kOhm [CAT25-513JALF]	51 kOhm [CR2512-JW-513ELF]	51 Ohm [4116R-2-510LF]	51 Ohm [4311R-101-510]
51 kOhm [CAY10-513J4LF]	51 kOhm [CRM2010-FX-5102ELF]	51 Ohm [4304M-102-510]	51 Ohm [4416P-1-510]
51 kOhm [CAY16-5102F4LF]	51 kOhm [CRM2512-FX-5102ELF]	51 Ohm [4304M-102-510LF]	51 Ohm [4416P-T01-510]
51 kOhm [CAY16-513J4LF]	51 kOhm [CRT0805-BW-5102ELF]		
51 kOhm [CAY17-513JALF]			

Multisim 14.1 Education Components

51 Ohm [4605X-101-510LF]	51 Ohm [4816P-T02-510]	51 Ohm [CAY16-510J2LF]	51 Ohm [CR1206-JW-510ELF]
51 Ohm [4606X-101-510LF]	51 Ohm [4816P-T02-510LF]	51 Ohm [CAY16-510J4LF]	51 Ohm [CR1206-JW-510GLF]
51 Ohm [4606X-102-510LF]	51 Ohm [4820P-1-510]	51 Ohm [CAY16-510J8LF]	51 Ohm [CR2010-JW-510ELF]
51 Ohm [4608X-101-510LF]	51 Ohm [4820P-1-510LF]	51 Ohm [CAY16-51R0F4LF]	51 Ohm [CR2512-JW-510ELF]
51 Ohm [4608X-102-510LF]	51 Ohm [4820P-T01-510]	51 Ohm [CAY17-510JALF]	51 Ohm [CRM0805-FX-51R0ELF]
51 Ohm [4609X-101-510LF]	51 Ohm [CAT10-510J4LF]	51 Ohm [CR0201-JW-510GLF]	51 Ohm [CRM1206-FX-51R0ELF]
51 Ohm [4610X-101-510LF]	51 Ohm [CAT16-510J2LF]	51 Ohm [CR0402-FX-51R0GLF]	51 Ohm [CRM2010-FX-51R0ELF]
51 Ohm [4610X-102-510LF]	51 Ohm [CAT16-510J4GLF]	51 Ohm [CR0402-JW-510GLF]	
51 Ohm [4814P-T01-510]	51 Ohm [CAT16-510J4LF]	51 Ohm [CR0603-FX-51R0ELF]	51 Ohm [CRM2512-FX-51R0ELF]
51 Ohm [4816P-1-510]	51 Ohm [CAT16-510J8LF]	51 Ohm [CR0603-JW-510ELF]	51 Ohm [CRM2512-JW-510ELF]
51 Ohm [4816P-1-510LF]	51 Ohm [CAT16-51R0F4LF]	51 Ohm [CR0603-JW-510GLF]	
51 Ohm [4816P-2-510]	51 Ohm [CAT16-51R0F8LF]	51 Ohm [CR0805-FX-51R0ELF]	51 Ohm [PWR220T-20-51R0F]
51 Ohm [4816P-2-510LF]	51 Ohm [CAT25-510JALF]	51 Ohm [CR0805-FX-51R0GLF]	51 Ohm [PWR2615W51R0F]
51 Ohm [4816P-T01-510]	51 Ohm [CAY10-510J2LF]	51 Ohm [CR0805-JW-510ELF]	51 pF [C0402C510K5GACT U]
51 Ohm [4816P-T01-510LF]	51 Ohm [CAY10-510J4LF]	51 Ohm [CR1206-FX-51R0ELF]	

Multisim 14.1 Education Components

51 pF [C0603C510K2GACT U]	51 pF [C1825C510KBGAC TU]	51.1 kOhm [CRT0603-FZ- 5112ELF]	51.1 Ohm [CRT0402-FZ- 51R1GLF]
51 pF [C0603C510K5GACT U]	51 pF [C2220C510KBGAC TU]	51.1 kOhm [CRT0603-PW- 5112ELF]	510 kOhm [4606X- 101-514LF] 510 kOhm [4608X- 101-514LF]
51 pF [C0805C510K1GACT U]	51 pF [C2225C510KBGAC TU]	51.1 kOhm [CRT0805-BY- 5112ELF]	510 kOhm [4608X- 102-514LF]
51 pF [C0805C510K2GACT U]	51.1 kOhm [CAY16- 5112F4LF]	51.1 kOhm [CRT0805-FY- 5112ELF]	510 kOhm [CAT10- 514J4LF]
51 pF [C0805C510K5GACT U]	51.1 kOhm [CR0402-FX- 5112GLF]	51.1 Ohm [CAT16- 51R1F4LF]	510 kOhm [CAY10- 514J4LF]
51 pF [C0805C510KBGAC TU]	51.1 kOhm [CR0603-FX- 5112ELF]	51.1 Ohm [CR0402- FX-51R1GLF]	510 kOhm [CAY16- 514J4LF]
51 pF [C0805C510KCGAC TU]	51.1 kOhm [CR0603-FX- 5112HLF]	51.1 Ohm [CR0603- FX-51R1ELF]	510 kOhm [CR0402-FX- 5103GLF]
51 pF [C1206C510K5GACT U]	51.1 kOhm [CR0805-FX- 5112ELF]	51.1 Ohm [CR0603- FX-51R1GLF]	510 kOhm [CR0402-JW- 514GLF]
51 pF [C1206C510KBGAC TU]	51.1 kOhm [CR1206-FX- 5112ELF]	51.1 Ohm [CR0805- FX-51R1ELF]	510 kOhm [CR0603-FX- 5103ELF]
51 pF [C1206C510KBGAC TU]	51.1 kOhm [CR1206-FX- 5112ELF]	51.1 Ohm [CR1206- FX-51R1ELF]	510 kOhm [CR0603-FX- 5103ELF]
51 pF [C1210C510KBGAC TU]	51.1 kOhm [CR2010- FX-51R1ELF]	51.1 Ohm [CR2010- FX-51R1ELF]	510 kOhm [CR0603-JW- 514ELF]
51 pF [C1210C510KBGAC TU]	51.1 kOhm [CR2512- FX-51R1ELF]	51.1 Ohm [CR2512- FX-51R1ELF]	510 kOhm [CR0805-FX- 5103ELF]
51 pF [C1812C510KBGAC TU]	51.1 kOhm [CRM0805-FX- 51R1ELF]	51.1 Ohm [CRM0805-FX- 51R1ELF]	510 kOhm [CR0805-JW- 514ELF]

Multisim 14.1 Education Components

510 kOhm [CR1206-FX- 5103ELF]	510 mOhm [CRL2512-FW- R510ELF]	510 Ohm [4116R-1- 511LF]	510 Ohm [4310R- 101-511LF]
510 kOhm [CR1206-JW- 514ELF]	510 mOhm [CRM0805-FX- R510ELF]	510 Ohm [4116R-2- 511]	510 Ohm [4310R- 102-511]
510 kOhm [CR2010-JW- 514ELF]	510 mOhm [CRM1206-FX- R510ELF]	510 Ohm [4306R- 101-511]	510 Ohm [4604X- 102-511LF]
510 mOhm [CRL0603-FW- R510ELF]	510 mOhm [CRM2010-FX- R510ELF]	510 Ohm [4308H- 101-511]	510 Ohm [4606X- 101-511LF]
510 mOhm [CRL0603-JW- R510ELF]	510 mOhm [CRM2512-FX- R510ELF]	510 Ohm [4308H- 102-511]	510 Ohm [4606X- 102-511LF]
510 mOhm [CRL0805-FW- R510ELF]	510 mOhm [CRM2512-JX- R510ELF]	510 Ohm [4308R- 101-511]	510 Ohm [4608X- 101-511LF]
510 mOhm [CRL0805-JW- R510ELF]	510 mOhm [PWR4318WR510JE]	510 Ohm [4308R- 101-511LF]	510 Ohm [4608X- 102-511LF]
510 mOhm [CRL1206-FW- R510ELF]	510 mOhm [PWR5322WR510JE]	510 Ohm [4308R- 102-511]	510 Ohm [4608X- AP2-511LF]
510 mOhm [CRL1206-JW- R510ELF]	510 Ohm [4114R-1- 511]	510 Ohm [4308R- 102-511LF]	510 Ohm [4609X- 101-511LF]
510 mOhm [CRL2010-FW- R510ELF]	510 Ohm [4114R-1- 511LF]	510 Ohm [4309R- 101-511]	510 Ohm [4610X- 101-511LF]
510 mOhm [CRL2010-JW- R510ELF]	510 Ohm [4114R-2- 511]	510 Ohm [4310M- 101-511]	510 Ohm [4610X- 102-511LF]
		510 Ohm [4310M- 101-511LF]	510 Ohm [4610X- AP1-511LF]
		510 Ohm [4310R- 101-511]	510 Ohm [4612H- 101-511LF]

Multisim 14.1 Education Components

510 Ohm [4814P-1-511]	510 Ohm [CAY10-511J2LF]	510 Ohm [CR2010-JW-511ELF]	510 pF [C0603C511K5HACT U]
510 Ohm [4814P-2-511]	510 Ohm [CAY10-511J4LF]	510 Ohm [CR2512-JW-511ELF]	510 pF [C0603C511K8GACT U]
510 Ohm [4814P-2-511LF]	510 Ohm [CAY16-511J4LF]	510 Ohm [CRM2512-FX-5100ELF]	510 pF [C0805C511K5GACT U]
510 Ohm [4814P-T02-511]	510 Ohm [CAY17-511JALF]	510 Ohm [CRM2512-JW-511ELF]	510 pF [C1206C511K1GACT U]
510 Ohm [4814P-T02-511LF]	510 Ohm [CR0201-FW-5100GLF]	510 Ohm [CRT0603-FY-5100ELF]	510 pF [C1206C511KBGAC TU]
510 Ohm [4816P-1-511]	510 Ohm [CR0402-FX-5100GLF]	510 Ohm [PWR220T-20-5100F]	510 pF [C1210C511KBGAC TU]
510 Ohm [4816P-1-511LF]	510 Ohm [CR0402-JW-511GLF]	510 pF [C0402C511K1HACT U]	510 pF [C1812C511KBGAC TU]
510 Ohm [4816P-2-511]	510 Ohm [CR0603-FX-5100ELF]	510 pF [C0402C511K3HACT U]	510 pF [C1825C511KBGAC TU]
510 Ohm [4816P-2-511LF]	510 Ohm [CR0603-JW-511ELF]	510 pF [C0402C511K5HACT U]	510 pF [C2220C511KBGAC TU]
510 Ohm [4816P-T01-511]	510 Ohm [CR0805-FX-5100ELF]	510 pF [C0603C511K1HACT U]	510 pF [C2225C511KBGAC TU]
510 Ohm [4816P-T01-511LF]	510 Ohm [CR0805-FX-5100GLF]	510 pF [C0603C511K3HACT U]	5103309-1
510 Ohm [4816P-T02-511]	510 Ohm [CR0805-JW-511ELF]	510 pF [C0603C511K5GACT U]	5103309-5
510 Ohm [CAT10-511J4LF]	510 Ohm [CR1206-FX-5100ELF]		5103309-6
510 Ohm [CAT16-511J4LF]	510 Ohm [CR1206-JW-511ELF]		
510 Ohm [CAT25-511JALF]	510 Ohm [CR2010-FX-5100ELF]		

Multisim 14.1 Education Components

5103309-7	511 Ohm [CR2010-FX-5110ELF]	52.3 Ohm [CR1206-FX-52R3ELF]	53.6 kOhm [CR0603-FX-5362GLF]
5103309-8			
5103310-1	511 Ohm [CR2512-FX-5110ELF]	5227222-3	53.6 kOhm [CR0805-FX-5362ELF]
5103310-5	511 Ohm [CRT0402-FZ-5110GLF]	5227677-1	
5103310-6		523 kOhm [CR0402-FX-5233GLF]	53.6 kOhm [CR1206-FX-5362ELF]
5103310-7	511 Ohm [CRT0603-BY-5110ELF]	523 kOhm [CR0603-FX-5233ELF]	53.6 kOhm [CRT0805-BY-5362ELF]
511 kOhm [CR0402-FX-5113GLF]	511 Ohm [CRT0805-CX-5110ELF]	523 kOhm [CR0805-FX-5233ELF]	53.6 Ohm [CR0603-FX-53R6ELF]
511 kOhm [CR0603-FX-5113ELF]	5-1814400-1	523 kOhm [CR1206-FX-5233ELF]	53.6 Ohm [CR0805-FX-53R6ELF]
511 kOhm [CR0805-FX-5113ELF]	52.3 kOhm [CR0402-FX-5232GLF]	523 Ohm [CR0402-FX-5230GLF]	53.6 Ohm [CR1206-FX-53R6ELF]
511 kOhm [CR1206-FX-5113ELF]	52.3 kOhm [CR0603-FX-5232ELF]	523 Ohm [CR0603-FX-5230ELF]	53.6 Ohm [CR2010-FX-53R6ELF]
511 Ohm [CAY16-5110F4LF]	52.3 kOhm [CR0805-FX-5232ELF]	523 Ohm [CR0805-FX-5230ELF]	532903-2
511 Ohm [CR0402-FX-5110GLF]	52.3 kOhm [CR1206-FX-5232ELF]	523 Ohm [CR1206-FX-5230ELF]	532903-6
511 Ohm [CR0603-FX-5110ELF]	52.3 kOhm [CRT0805-BW-5232ELF]	53.6 kOhm [CR0402-FX-5362GLF]	534206-5
511 Ohm [CR0805-FX-5110ELF]	52.3 Ohm [CR0603-FX-52R3ELF]	53.6 kOhm [CR0603-FX-5362ELF]	534237-3
511 Ohm [CR1206-FX-5110ELF]	52.3 Ohm [CR0805-FX-52R3ELF]		534237-6
			534237-8
			536 kOhm [CR0603-FX-5363ELF]

Multisim 14.1 Education Components

536 kOhm [CR0805-FX- 5363ELF]	54.9 Ohm [CR0402- FX-54R9GLF]	549 Ohm [CR1206- FX-5490ELF]	56 kOhm [4116R-1- 563LF]
536 kOhm [CR1206-FX- 5363ELF]	54.9 Ohm [CR0603- FX-54R9ELF]	549 Ohm [CRT1206-BV- 5490ELF]	56 kOhm [4116R-2- 563]
536 Ohm [CR0402- FX-5360GLF]	54.9 Ohm [CR0805- FX-54R9ELF]	549 Ohm [CRT1206-BW- 5490ELF]	56 kOhm [4116R-2- 563LF]
536 Ohm [CR0603- FX-5360ELF]	54.9 Ohm [CR1206- FX-54R9ELF]	549 Ohm [CRT1206-BY- 5490ELF]	56 kOhm [4306R- 101-563]
536 Ohm [CR0805- FX-5360ELF]	540 nH [SRP1205- R30Y]	549 Ohm [CRA2512-JZ- R055ELF]	56 kOhm [4306R- 101-563LF]
536 Ohm [CR1206- FX-5360ELF]	5414337-1	55 mOhm [CRA2512-JZ- R055ELF]	56 kOhm [4306R- 102-563]
54.9 kOhm [CAY16- 5492F4LF]	549 kOhm [CR0201-FW- 5493GLF]	55 Ohm [4416P-2- 550]	56 kOhm [4306R- 102-563LF]
54.9 kOhm [CR0402-FX- 5492GLF]	549 kOhm [CR0402-FX- 5493GLF]	555_Timer	56 kOhm [4308R- 101-563]
54.9 kOhm [CR0603-FX- 5492ELF]	549 kOhm [CR0603-FX- 5493ELF]	555_TIMER_RATED	56 kOhm [4308R- 101-563LF]
54.9 kOhm [CR0805-FX- 5492ELF]	549 kOhm [CR0805-FX- 5493ELF]	555_VIRTUAL	56 kOhm [4308R- 102-563]
54.9 kOhm [CR1206-FX- 5492ELF]	549 kOhm [CR1206-FX- 5493ELF]	5558067-1	56 kOhm [4308R- 102-563LF]
54.9 Ohm [CAY16- 54R9F4LF]	549 Ohm [CR0402- FX-5490GLF]	56 kOhm [4114R-1- 563]	56 kOhm [4308R- 102-563LF]
54.9 Ohm [CR0201- FW-54R9GLF]	549 Ohm [CR0603- FX-5490ELF]	56 kOhm [4114R-1- 563LF]	56 kOhm [4310R- 101-563]
	549 Ohm [CR0805- FX-5490ELF]	56 kOhm [4114R-2- 563]	56 kOhm [4310R- 101-563LF]
		56 kOhm [4114R-2- 563LF]	56 kOhm [4310R- 102-563]
		56 kOhm [4116R-1- 563]	56 kOhm [4310R- 102-563LF]

Multisim 14.1 Education Components

56 kOhm [4420P-2-563]	56 kOhm [4814P-T02-563]	56 kOhm [CAY16-5602F4LF]	56 kOhm [CR1206-JW-563GLF]
56 kOhm [4420P-T02-563]	56 kOhm [4816P-1-563]	56 kOhm [CAY16-563J4LF]	56 kOhm [CR2010-JW-563ELF]
56 kOhm [4604X-102-563LF]	56 kOhm [4816P-1-563LF]	56 kOhm [CAY16-563J8LF]	56 kOhm [CRT0603-AX-5602ELF]
56 kOhm [4605X-101-563LF]	56 kOhm [4816P-2-563]	56 kOhm [CAY17-563JALF]	56 kOhm [PWR163S-25-5602F]
56 kOhm [4606X-101-563LF]	56 kOhm [4816P-2-563LF]	56 kOhm [CR0201-FW-5602GLF]	56 kOhm [PWR220T-20-5602F]
56 kOhm [4606X-102-563LF]	56 kOhm [4816P-T01-563]	56 kOhm [CR0402-FX-5602GLF]	56 mF [C0805C569KKBGAC TU]
56 kOhm [4608M-102-563LF]	56 kOhm [4816P-T01-563LF]	56 kOhm [CR0402-JW-563GLF]	56 nF [C0402C563K4RACT U]
56 kOhm [4608X-101-563LF]	56 kOhm [4816P-T02-563]	56 kOhm [CR0603-FX-5602ELF]	56 nF [C0402C563K8RACT U]
56 kOhm [4608X-102-563LF]	56 kOhm [4816P-T02-563LF]	56 kOhm [CR0603-JW-563ELF]	56 nF [C0402C563K9RACT U]
56 kOhm [4608X-AP2-563LF]	56 kOhm [4820P-2-563]	56 kOhm [CR0603-JW-563GLF]	56 nF [C0603C563K3RACT U]
56 kOhm [4609X-101-563LF]	56 kOhm [CAT10-563J4LF]	56 kOhm [CR0805-FX-5602ELF]	56 nF [C0603C563K4RACT U]
56 kOhm [4610X-101-563LF]	56 kOhm [CAT16-5602F4LF]	56 kOhm [CR0805-FX-5602GLF]	56 nF [C0603C563K5RACT U]
56 kOhm [4610X-102-563LF]	56 kOhm [CAT16-563J4LF]	56 kOhm [CR0805-JW-563ELF]	56 nF [C0603C563K5RACT U]
56 kOhm [4612X-102-563LF]	56 kOhm [CAT16-563J8LF]	56 kOhm [CR1206-FX-5602ELF]	56 nF [C0603C563K5RACT U]
56 kOhm [4814P-2-563]	56 kOhm [CAT25-563JALF]	56 kOhm [CR1206-JW-563ELF]	

Multisim 14.1 Education Components

56 nF [C0805C563K1RACT U]	56 nF [C1206C563K3RACT U]	56 nF [C1210C563K1RACT U]	56 nF [C1812C563K5HACT U]
56 nF [C0805C563K2RACT U]	56 nF [C1206C563K5HACT U]	56 nF [C1210C563K2RACT U]	56 nF [C2220C563K1GACT U]
56 nF [C0805C563K3RACT U]	56 nF [C1206C563K5RACT U]	56 nF [C1210C563K3HACT U]	56 nF [C2220C563K2GACT U]
56 nF [C0805C563K4RACT U]	56 nF [C1206C563KARACT U]	56 nF [C1210C563K5GACT U]	56 nF [C2220C563K5GACT U]
56 nF [C0805C563K5RACT U]	56 nF [C1206C563M5UAC TU]	56 nF [C1210C563K5HACT U]	56 nF [GMC5.7563K50J31 TR12]
56 nF [C0805C563K8RACT U]	56 nF [C1206F563K1RACT U]	56 nF [C1210C563K5RACT U]	56 nF [GMC7.3562K250K3 1TR12]
56 nF [C0805F563K3RACT U]	56 nF [C1206F563K3RACT U]	56 nF [C1210C563KARACT U]	56 nF [GMC7.3563K63K31 TR12]
56 nF [C0805F563K4RACT U]	56 nF [C1206F563K4RACT U]	56 nF [C1812C563K1GACT U]	56 nF [MDC10563K100A5 2P3TUBE]
56 nF [C0805F563K5RACT U]	56 nF [C1206F563K5RACT U]	56 nF [C1812C563K1HACT U]	56 nF [MDC10563K250A5 2P3TUBE]
56 nF [C1206C563K1RACT U]	56 nF [C1210C563K1GACT U]	56 nF [C1812C563K1RACT U]	56 nF [MDC10563K400A5 2P3TUBE]
56 nF [C1206C563K3HACT U]	56 nF [C1210C563K1HACT U]	56 nF [C1812C563K5GACT U]	56 nF [MDC10563K50A52 P3TUBE]

Multisim 14.1 Education Components

56 nF [MDC10563K630A5 2P3TUBE]	56 Ohm [4114R-1- 560]	56 Ohm [4308R- 102-560]	56 Ohm [4420P-2- 560]
56 nF [MDC15563K100B5 3P3TUBE]	56 Ohm [4114R-1- 560LF]	56 Ohm [4308R- 102-560LF]	56 Ohm [4420P- T01-560]
56 nF [MDC15563K250B5 3P3TUBE]	56 Ohm [4116R-1- 560]	56 Ohm [4309R- 101-560]	56 Ohm [4420P- T02-560]
56 nF [MDC15563K250B5 3P3TUBE]	56 Ohm [4116R-1- 560LF]	56 Ohm [4310H- 101-560]	56 Ohm [4604X- 101-560LF]
56 nF [MDC15563K400B5 3P3TUBE]	56 Ohm [4116R-2- 560]	56 Ohm [4310H- 101-560LF]	56 Ohm [4604X- 102-560LF]
56 nF [MDC15563K50B53 P3TUBE]	56 Ohm [4116R-2- 560LF]	56 Ohm [4310M- 102-560]	56 Ohm [4605M- 101-560LF]
56 nF [MDC15563K50B53 P3TUBE]	56 Ohm [4304M- 102-560]	56 Ohm [4310M- 102-560LF]	56 Ohm [4605X- 101-560LF]
56 nF [MDC15563K630B5 3P3TUBE]	56 Ohm [4306R- 101-560]	56 Ohm [4310R- 101-560]	56 Ohm [4606M- 101-560LF]
56 nF [MDK15563K250B5 3P3TUBE]	56 Ohm [4306R- 101-560LF]	56 Ohm [4310R- 101-560LF]	56 Ohm [4606X- 101-560LF]
56 nF [MDK15563K250B5 3P3TUBE]	56 Ohm [4306R- 102-560]	56 Ohm [4310R- 102-560]	56 Ohm [4606X- 102-560LF]
56 nF [MDK15563K400B5 3P3TUBE]	56 Ohm [4306R- 102-560LF]	56 Ohm [4310R- 102-560LF]	56 Ohm [4607X- 101-560LF]
56 nF [MDK15563K50B53 P3TUBE]	56 Ohm [4308M- 102-560]	56 Ohm [4416P-1- 560]	56 Ohm [4608X- 101-560LF]
56 nF [MDS15563K400B5 3P3TUBE]	56 Ohm [4308M- 102-560LF]	56 Ohm [4416P-2- 560]	56 Ohm [4608X- 102-560LF]
56 nF [MDS15563K50B53 P3TUBE]	56 Ohm [4308R- 101-560]	56 Ohm [4416P- T01-560]	56 Ohm [4608X- AP2-560LF]
56 nF [MDS15563K50B53 P3TUBE]	56 Ohm [4308R- 101-560LF]	56 Ohm [4420P-1- 560]	56 Ohm [4609X- 101-560LF]

Multisim 14.1 Education Components

56 Ohm [4610X-101-560LF]	56 Ohm [CAT10-560J4LF]	56 Ohm [CR0805-FX-56R0GLF]	56 Ohm [PWR220T-20-56R0J]
56 Ohm [4610X-102-560LF]	56 Ohm [CAT16-560J4LF]	56 Ohm [CR0805-JW-560ELF]	56 Ohm [PWR221T-30-56R0F]
56 Ohm [4612X-102-560LF]	56 Ohm [CAT16-560J8LF]	56 Ohm [CR0805-JW-560GLF]	56 Ohm [PWR221T-30-56R0J]
56 Ohm [4614X-102-560LF]	56 Ohm [CAT16-56R0F4LF]	56 Ohm [CR1206-FX-56R0ELF]	56 Ohm [PWR263S-20-56R0F]
56 Ohm [4814P-T01-560]	56 Ohm [CAT25-560JALF]	56 Ohm [CR1206-FX-56R0GLF]	56 Ohm [PWR263S-20-56R0FE]
56 Ohm [4816P-1-560]	56 Ohm [CAY10-560J4LF]	56 Ohm [CR1206-JW-560ELF]	56 Ohm [PWR263S-20-56R0J]
56 Ohm [4816P-1-560LF]	56 Ohm [CAY16-560J4LF]	56 Ohm [CR2512-FX-56R0ELF]	56 Ohm [PWR263S-35-56R0F]
56 Ohm [4816P-2-560]	56 Ohm [CAY16-560J8LF]	56 Ohm [CR2512-JW-560ELF]	56 Ohm [PWR263S-35-56R0J]
56 Ohm [4816P-2-560LF]	56 Ohm [CAY16-56R0F4LF]	56 Ohm [CRM2512-FX-56R0ELF]	56 pF [C0201C560K3GACT U]
56 Ohm [4816P-T01-560]	56 Ohm [CAY17-560JALF]	56 Ohm [CRT0603-BY-56R0ELF]	56 pF [C0201C560K8GACT U]
56 Ohm [4816P-T01-560LF]	56 Ohm [CR0402-FX-56R0GLF]	56 Ohm [PWR163S-25-56R0F]	56 pF [C0402C560K3GACT U]
56 Ohm [4816P-T02-560]	56 Ohm [CR0402-JW-560GLF]	56 Ohm [PWR163S-25-56R0J]	
56 Ohm [4816P-T02-560LF]	56 Ohm [CR0603-FX-56R0ELF]	56 Ohm [PWR220T-20-56R0F]	
56 Ohm [4818P-T01-560]	56 Ohm [CR0603-JW-560ELF]		
56 Ohm [4820P-T01-560]	56 Ohm [CR0805-FX-56R0ELF]		

Multisim 14.1 Education Components

56 pF [C0402C560K5GACT U]	56 pF [C1206C560K1GACT U]	56 pF [CA064C560K5GAC TU]	56 uF [EEHZC1E560P]
56 pF [C0402C560K8GACT U]	56 pF [C1206C560K2GACT U]	56 uF [A700D566M008AT E015]	56 uF [EEHZC1J560P]
56 pF [C0603C560K1GACT U]	56 pF [C1206C560K5GACT U]	56 uF [A700D566M008AT E018]	56 uF [T520T566M2R5AT E040]
56 pF [C0603C560K2GACT U]	56 pF [C1206C560KBGAC TU]	56 uF [A700D566M010AT E015]	56 uF [T520T566M2R5AT E070]
56 pF [C0603C560K3GACT U]	56 pF [C1206C560KDGAC TU]	56 uF [A700D566M010AT E018]	56 uH [SDE0403A- 560K]
56 pF [C0603C560K5GACT U]	56 pF [C1210C560KBGAC TU]	56 uF [A700V566M006AT E018]	56 uH [SDE0805A- 560K]
56 pF [C0805C560K1GACT U]	56 pF [C1812C560KBGAC TU]	56 uF [A700V566M006AT E025]	56 uH [SDE1006A- 560K]
56 pF [C0805C560K2GACT U]	56 pF [C1812C560KHGAC TU]	56 uF [A700V566M006AT E028]	56 uH [SDR0403- 560KL]
56 pF [C0805C560K5GACT U]	56 pF [C1825C560KBGAC TU]	56 uF [EEFCX1D560R]	56 uH [SDR0503- 560KL]
56 pF [C0805C560KBGAC TU]	56 pF [C2220C560KBGAC TU]	56 uF [EEFHX1D560R]	56 uH [SDR0603- 560KL]
56 pF [C0805C560KDGAC TU]	56 pF [C2225C560KBGAC TU]	56 uF [EEHZA1E560P]	56 uH [SDR0604- 560KL]
		56 uF [EEHZA1J560P]	56 uH [SDR0703- 560KL]
			56 uH [SDR0805- 560KL]

Multisim 14.1 Education Components

56 uH [SDR0906-560KL]	56 uH [SRR1005-560Y]	56 uH [SRR6038-560Y]	56.2 kOhm [CRT0603-BY-5622ELF]
56 uH [SDR1006-560KL]	56 uH [SRR1205-560YL]	56 uH [SRR6040A-560M]	56.2 kOhm [CRT1206-FZ-5622ELF]
56 uH [SDR1105-560KL]	56 uH [SRR1206-560YL]	56 uH [SRR7045-560M]	56.2 Ohm [CAT16-56R2F4LF]
56 uH [SDR1307-560KL]	56 uH [SRR1208-560YL]	56 uH [SRU1028-560Y]	56.2 Ohm [CAY16-56R2F4LF]
56 uH [SDR1307A-560K]	56 uH [SRR1210-560M]	56 uH [SRU1028A-560Y]	56.2 Ohm [CR0201-FW-56R2GLF]
56 uH [SRP1770TA-560M]	56 uH [SRR1210A-560M]	56 uH [SRU1048-560Y]	56.2 Ohm [CR0402-FX-56R2GLF]
56 uH [SRP7050TA-560M]	56 uH [SRR1240-560M]	56 uH [SRU1048A-560Y]	56.2 Ohm [CR0603-FX-56R2ELF]
56 uH [SRR0735A-560M]	56 uH [SRR1260-560M]	56.2 kOhm [CAY16-5622F4LF]	56.2 Ohm [CR0805-FX-56R2ELF]
56 uH [SRR0745A-560M]	56 uH [SRR1260A-560M]	56.2 kOhm [CR0402-FX-5622GLF]	56.2 Ohm [CR1206-FX-56R2ELF]
56 uH [SRR0804-560K]	56 uH [SRR1280-560M]	56.2 kOhm [CR0603-FX-5622ELF]	56.2 Ohm [CR2512-FX-56R2ELF]
56 uH [SRR0805-560K]	56 uH [SRR4018-560Y]	56.2 kOhm [CR0805-FX-5622ELF]	56.2 Ohm [CRM1206-FX-56R2ELF]
56 uH [SRR0905-560Y]	56 uH [SRR4028-560Y]	56.2 kOhm [CR1206-FX-5622ELF]	56.2 Ohm [CRT0402-FZ-56R2GLF]
56 uH [SRR0906-560ML]	56 uH [SRR5018-560Y]	56.2 kOhm [CRT0402-FZ-5622GLF]	
56 uH [SRR0908-560ML]	56 uH [SRR5028-560Y]		
56 uH [SRR1003-560M]	56 uH [SRR6028-560Y]		

Multisim 14.1 Education Components

560 kOhm [4114R-1-564]	560 kOhm [4310M-101-564]	560 kOhm [4816P-2-564LF]	560 kOhm [CR0603-JW-564ELF]
560 kOhm [4114R-1-564LF]	560 kOhm [4310M-101-564LF]	560 kOhm [4816P-T01-564]	560 kOhm [CR0805-FX-5603ELF]
560 kOhm [4114R-2-564]	560 kOhm [4310R-101-564]	560 kOhm [4816P-T01-564LF]	560 kOhm [CR0805-JW-564ELF]
560 kOhm [4116R-1-564]	560 kOhm [4310R-101-564LF]	560 kOhm [4816P-T02-564]	560 kOhm [CR1206-FX-5603ELF]
560 kOhm [4116R-1-564LF]	560 kOhm [4310R-102-564]	560 kOhm [4816P-T02-564LF]	560 kOhm [CR1206-JW-564ELF]
560 kOhm [4116R-2-564]	560 kOhm [4606X-101-564LF]	560 kOhm [CAT16-564J4LF]	560 kOhm [CRM2512-JW-564ELF]
560 kOhm [4116R-2-564LF]	560 kOhm [4606X-102-564LF]	560 kOhm [CAT25-564JALF]	560 mOhm [CRL0603-FW-R560ELF]
560 kOhm [4306R-101-564]	560 kOhm [4608X-101-564LF]	560 kOhm [CAY10-564J4LF]	560 mOhm [CRL0603-JW-R560ELF]
560 kOhm [4306R-102-564]	560 kOhm [4608X-102-564LF]	560 kOhm [CAY16-5603F4LF]	560 mOhm [CRL0805-FW-R560ELF]
560 kOhm [4306R-102-564LF]	560 kOhm [4609X-101-564LF]	560 kOhm [CAY16-564J4LF]	560 mOhm [CRL0805-JW-R560ELF]
560 kOhm [4308R-101-564]	560 kOhm [4610X-101-564LF]	560 kOhm [CAY16-564J8LF]	560 mOhm [CRL1206-FW-R560ELF]
560 kOhm [4308R-101-564LF]	560 kOhm [4610X-102-564LF]	560 kOhm [CR0402-FX-5603GLF]	
560 kOhm [4308R-102-564]	560 kOhm [4816P-1-564]	560 kOhm [CR0402-JW-564GLF]	
560 kOhm [4308R-102-564LF]	560 kOhm [4816P-1-564LF]	560 kOhm [CR0603-FX-5603ELF]	
560 kOhm [4310H-101-564]	560 kOhm [4816P-2-564]		

Multisim 14.1 Education Components

560 mOhm [CRL1206-JW-R560ELF]	560 nF [C1206C564K3RACT U]	560 nF [C1812F564K5RACT U]	560 nF [MDC10564K50A52 P3TUBE]
560 mOhm [CRL2010-FW-R560ELF]	560 nF [C1206C564K4RACT U]	560 nF [C1825C564K5RACT U]	560 nF [MDC15564K100B5 3P3TUBE]
560 mOhm [CRL2010-JW-R560ELF]	560 nF [C1206C564K5RACT U]	560 nF [C1825C564KARACT U]	560 nF [MDC15564K250B5 3P3TUBE]
560 mOhm [CRL2512-FW-R560ELF]	560 nF [C1206F564K4RACT U]	560 nF [C2220C564K1RACT U]	560 nF [MDC15564K50B53 P3TUBE]
560 mOhm [PWR4318WR560JE]	560 nF [C1210C564K5RACT U]	560 nF [C2220C564K5RACT U]	560 nF [MDK15564K100B5 3P3TUBE]
560 mOhm [PWR4525WR560J]	560 nF [C1210F564K3RACT U]	560 nF [C2220C564KARACT U]	560 nF [MDK15564K50B53 P3TUBE]
560 mOhm [PWR4525WR560JE]	560 nF [C1210F564K4RACT U]	560 nF [C2225C564K5RACT U]	560 nH [SRP1038A- R56M]
560 nF [C0603C564K8PACT U]	560 nF [C1210F564K5RACT U]	560 nF [C2225C564KARACT U]	560 nH [SRP1040- R56M]
560 nF [C0805C564K3RACT U]	560 nF [C1812C564K5RACT U]	560 nF [MDC10564K100A5 2P3TUBE]	560 nH [SRP1250- R56M]
560 nF [C0805C564K4RACT U]	560 nF [C1812F564K1RACT U]	560 nF [MDC10564K250A5 4P3TUBE]	560 nH [SRP1265A- R56M]
560 nF [C0805C564K8RACT U]	560 nF [C1812F564K3RACT U]	560 nF [MDC10564K250A5 4P4TUBE]	560 nH [SRP4012- R56M]
			560 nH [SRP4020- R56M]
			560 nH [SRP4020TA-R56M]

Multisim 14.1 Education Components

560 nH [SRP6540-R56M]	560 Ohm [4306R-101-561LF]	560 Ohm [4310H-101-561LF]	560 Ohm [4606H-101-561LF]
560 nH [SRP7028A-R56M]	560 Ohm [4306R-102-561]	560 Ohm [4310M-101-561]	560 Ohm [4606M-101-561LF]
560 nH [SRP7030-R56FM]	560 Ohm [4306R-102-561LF]	560 Ohm [4310M-101-561LF]	560 Ohm [4606X-101-561LF]
560 nH [SRP7050TA-R56M]	560 Ohm [4308H-101-561]	560 Ohm [4310R-101-561]	560 Ohm [4606X-102-561LF]
560 Ohm [4114R-1-561]	560 Ohm [4308H-101-561LF]	560 Ohm [4310R-101-561LF]	560 Ohm [4607X-101-561LF]
560 Ohm [4114R-1-561LF]	560 Ohm [4308H-102-561]	560 Ohm [4310R-102-561]	560 Ohm [4608M-102-561LF]
560 Ohm [4114R-2-561]	560 Ohm [4308H-102-561LF]	560 Ohm [4310R-102-561LF]	560 Ohm [4608X-101-561LF]
560 Ohm [4114R-2-561LF]	560 Ohm [4308M-101-561]	560 Ohm [4416P-1-561]	560 Ohm [4608X-102-561LF]
560 Ohm [4116R-1-561]	560 Ohm [4308R-101-561]	560 Ohm [4416P-1-561LF]	560 Ohm [4608X-AP2-561LF]
560 Ohm [4116R-1-561LF]	560 Ohm [4308R-101-561LF]	560 Ohm [4416P-T01-561]	560 Ohm [4609X-101-561LF]
560 Ohm [4116R-2-561]	560 Ohm [4308R-102-561]	560 Ohm [4420P-2-561]	560 Ohm [4610H-101-561LF]
560 Ohm [4116R-2-561LF]	560 Ohm [4308R-102-561LF]	560 Ohm [4420P-T02-561]	560 Ohm [4610X-101-561LF]
560 Ohm [4306H-102-561]	560 Ohm [4309R-101-561]	560 Ohm [4604X-102-561LF]	560 Ohm [4610X-102-561LF]
560 Ohm [4306M-101-561]	560 Ohm [4309R-101-561LF]	560 Ohm [4605M-101-561LF]	560 Ohm [4610X-AP1-561LF]
560 Ohm [4306R-101-561]	560 Ohm [4310H-101-561]	560 Ohm [4605X-101-561LF]	560 Ohm [4612X-101-561LF]

Multisim 14.1 Education Components

560 Ohm [4612X-102-561LF]	560 Ohm [CAT16-5600F4LF]	560 Ohm [CR0805-FX-5600ELF]	560 pF [C0402C561K3GACT U]
560 Ohm [4814P-1-561]	560 Ohm [CAT16-561J4LF]	560 Ohm [CR0805-FX-5600GLF]	560 pF [C0402C561K3HACT U]
560 Ohm [4814P-T01-561]	560 Ohm [CAT16-561J8LF]	560 Ohm [CR0805-JW-561ELF]	560 pF [C0402C561K3RACT U]
560 Ohm [4814P-T01-561LF]	560 Ohm [CAT25-561JALF]	560 Ohm [CR0805-JW-561GLF]	560 pF [C0402C561K3RACT U]
560 Ohm [4816P-1-561]	560 Ohm [CAY10-561J4LF]	560 Ohm [CR1206-FX-5600ELF]	560 pF [C0402C561K4RACT U]
560 Ohm [4816P-1-561LF]	560 Ohm [CAY16-5600F4LF]	560 Ohm [CR1206-JW-561ELF]	560 pF [C0402C561K5HACT U]
560 Ohm [4816P-2-561]	560 Ohm [CAY16-561J4LF]	560 Ohm [CR2010-JW-561ELF]	560 pF [C0402C561K5HACT U]
560 Ohm [4816P-2-561LF]	560 Ohm [CAY16-561J8LF]	560 Ohm [CR2512-JW-561ELF]	560 pF [C0402C561K5RACT U]
560 Ohm [4816P-T01-561]	560 Ohm [CAY17-561JALF]	560 Ohm [PWR163S-25-5600FE]	560 pF [C0402C561K8RACT U]
560 Ohm [4816P-T01-561LF]	560 Ohm [CR0402-FX-5600GLF]	560 Ohm [PWR163S-25-5600J]	560 pF [C0603C561K1HACT U]
560 Ohm [4816P-T02-561]	560 Ohm [CR0402-JW-561GLF]	560 Ohm [PWR221T-30-5600F]	560 pF [C0603C561K1RACT U]
560 Ohm [4816P-T02-561LF]	560 Ohm [CR0603-FX-5600ELF]	560 Ohm [PWR5322W5600FE]	560 pF [C0603C561K2RACT U]
560 Ohm [4820P-2-561]	560 Ohm [CR0603-FX-5600HLF]	560 pF [C0402C561K1HACT U]	560 pF [C0603C561K3HACT U]
560 Ohm [4820P-T01-561]	560 Ohm [CR0603-JW-561ELF]		
560 Ohm [4820P-T02-561]	560 Ohm [CR0603-JW-561GLF]		

Multisim 14.1 Education Components

560 pF [C0603C561K3RACT U]	560 pF [C0805C561K5RACT U]	560 pF [CA064C561K2RACT U]	560 uF [EEFGX0D561R]
560 pF [C0603C561K4RACT U]	560 pF [C0805C561K8RACT U]	560 uF [16SVPF560M]	560 uF [EEFHX0D561R]
560 pF [C0603C561K5GACT U]	560 pF [C1206C561K1GACT U]	560 uF [2R5SVPC560M]	560 uF [EEFHX0D561R4]
560 pF [C0603C561K5HACT U]	560 pF [C1206C561K2GACT U]	560 uF [2SEPC560MW]	560 uF [EEFLX0D561R]
560 pF [C0603C561K5RACT U]	560 pF [C1206C561K5GACT U]	560 uF [2SEPC560MZ]	560 uF [EEFSX0D561E4]
560 pF [C0603C561K8RACT U]	560 pF [C1206C561KBGAC TU]	560 uF [4SEPC560MW]	560 uF [T530D567M2R5AT E005]
560 pF [C0805C561K1GACT U]	560 pF [C1210C561KBGAC TU]	560 uF [4SVP560M]	560 uH [SDE1006A- 561K]
560 pF [C0805C561K1RACT U]	560 pF [C1812C561KBGAC TU]	560 uF [4SVPC560M]	560 uH [SDR0302- 561KL]
560 pF [C0805C561K2RACT U]	560 pF [C1825C561KBGAC TU]	560 uF [4SVPC560MX]	560 uH [SDR0403- 561KL]
560 pF [C0805C561K4RACT U]	560 pF [C2220C561KBGAC TU]	560 uF [6SEPC560MW]	560 uH [SDR0503- 561KL]
560 pF [C0805C561K5GACT U]	560 pF [C2225C561KBGAC TU]	560 uF [6SEPC560MX]	560 uH [SDR0604- 561KL]
		560 uF [EEFCX0D561R]	560 uH [SDR0703- 561KL]
		560 uF [EEFGX0D561L]	560 uH [SDR0805- 561KL]
			560 uH [SDR0906- 561KL]

Multisim 14.1 Education Components

560 uH [SDR1006-561KL]	560 uH [SRR1260-561K]	562 Ohm [CR0603-FX-5620GLF]	57.6 Ohm [CR1206-FX-57R6ELF]
560 uH [SDR1307-561KL]	560 uH [SRR1260A-561K]	562 Ohm [CR0805-FX-5620ELF]	571-0100
560 uH [SDR1307A-561K]	560 uH [SRR1280-561K]	562 Ohm [CR1206-FX-5620ELF]	571-0200
560 uH [SRR0735A-561M]	560 uH [SRR4028-561Y]	562 Ohm [CRM1206-FX-5620ELF]	571-0300
560 uH [SRR0745A-561M]	560 uH [SRR5028-561Y]	562 Ohm [CRT0402-FZ-5620GLF]	571-0400
560 uH [SRR0805-561K]	560 uH [SRR7045-561M]	562 Ohm [CRT1206-FZ-5620ELF]	571-0500
560 uH [SRR0906-561YL]	560 uH [SRU1048-561Y]	562 Ohm [CRT1206-FZ-5620ELF]	571-0600
560 uH [SRR0908-561YL]	562 kOhm [CR0402-FX-5623GLF]	5687169-9	571-0700
560 uH [SRR1005-561K]	562 kOhm [CR0603-FX-5623ELF]	57.6 kOhm [CR0402-FX-5762GLF]	576 kOhm [CR0402-FX-5763GLF]
560 uH [SRR1205-561KL]	562 kOhm [CR0805-FX-5623ELF]	57.6 kOhm [CR0603-FX-5762ELF]	576 kOhm [CR0805-FX-5763ELF]
560 uH [SRR1206-561KL]	562 kOhm [CR1206-FX-5623ELF]	57.6 kOhm [CR0805-FX-5762ELF]	576 kOhm [CR1206-FX-5763ELF]
560 uH [SRR1208-561KL]	562 Ohm [CAY16-5620F4LF]	57.6 Ohm [CR0603-FX-57R6ELF]	576 Ohm [CR0402-FX-5760GLF]
560 uH [SRR1210-561M]	562 Ohm [CR0402-FX-5620GLF]	57.6 Ohm [CR0805-FX-5760ELF]	576 Ohm [CR0603-FX-5760ELF]
560 uH [SRR1210A-561M]	562 Ohm [CR0603-FX-5620ELF]		576 Ohm [CR0805-FX-5760ELF]
560 uH [SRR1240-561K]			576 Ohm [CR1206-FX-5760ELF]

Multisim 14.1 Education Components

576 Ohm [CRT1206-BY- 5760ELF]	590 kOhm [CR0603-FX- 5903ELF]	5KP58A-E3/54	5P4S
59 kOhm [CR0402- FX-5902GLF]	590 kOhm [CR0805-FX- 5903ELF]	5KP60A-E3/54	5P5S
59 kOhm [CR0603- FX-5902ELF]	590 kOhm [CR1206-FX- 5903ELF]	5KP85A-E3/54	5POS_ROTARY
59 kOhm [CR0805- FX-5902ELF]	590 Ohm [CR0402- FX-5900GLF]	5Line_Bussed	5U4GB
59 kOhm [CR1206- FX-5902ELF]	590 Ohm [CR0603- FX-5900ELF]	5Line_Isolated	5V_1W
59 kOhm [CRM2010-FX- 5902ELF]	590 Ohm [CR0805- FX-5900ELF]	5LN01C-TB-E	5V3A
59 Ohm [CR0402- FX-59R0GLF]	590 Ohm [CR1206- FX-5900ELF]	5LN01C-TB-H	5V4GA
59 Ohm [CR0603- FX-59R0ELF]	5AR4	5LN01M-TL-E	5Y3GT
59 Ohm [CR0805- FX-59R0ELF]	5EQ100	5LN01M-TL-H	6 kOhm [4116R-1- 602]
59 Ohm [CR1206- FX-59R0ELF]	5KP10A-E3/54	5LN01SP-AC	6 kOhm [4116R-1- 602LF]
59 Ohm [CRM2512-FX- 59R0ELF]	5KP16A-E3/54	5LN01SS-TL-E	6 kOhm [4116R-2- 602]
59 Ohm [CRT0402- FZ-59R0GLF]	5KP18A-E3/54	5LN01SS-TL-H	6 mOhm [CRE2512- FZ-R006E-2]
590 kOhm [CR0402-FX- 5903GLF]	5KP22A-E3/54	5LN01S-TL-E	6 mOhm [CRE2512- FZ-R006E-3]
	5KP24A-E3/54	5LP01C-TB-E	6 mOhm [CRE2512- FZ-R006E-3]
	5KP28A-E3/54	5LP01C-TB-H	6 mOhm [CRF2512- FX-R006ELF]
	5KP30A-E3/54	5LP01M-TL-E	6 mOhm [CRM2512-FX- 59R0ELF]
	5KP33A-E3/54	5LP01M-TL-H	6 mOhm [PWR4412- 2SBR0060F]
	5KP40A-E3/54	5LP01SP	6 Ohm [PWR221T- 50-6R00F]
	5KP48A-E3/54	5LP01SP-AC	6 Ohm [PWR4525W6R00F]
		5LP01SS-TL-E	6 Ohm [PWR4525W6R00F E]
		5LP01SS-TL-H	
		5LP01S-TL-E	
		5P1S	
		5P2S	
		5P3S	

Multisim 14.1 Education Components

6 uH [SRN6028-6ROM]	6.1 uH [SRR1260A-6R1Y]	6.2 kOhm [4309R-101-622LF]	6.2 kOhm [CR1206-FX-6201ELF]
6 uH [SRP1250-6ROM]	6.1 uH [SRR1280-6R1Y]	6.2 kOhm [4310R-101-622]	6.2 kOhm [CR1206-JW-622ELF]
6 uH [SRR6028-6ROY]	6.19 kOhm [CR0402-FX-6191GLF]	6.2 kOhm [4604X-101-622LF]	6.2 MOhm [4116R-1-625]
6 uH [SRU2016-6ROY]	6.19 kOhm [CR0603-FX-6191ELF]	6.2 kOhm [4609X-101-622LF]	6.2 MOhm [4116R-1-625LF]
6.04 kOhm [CAY16-6041F4LF]	6.19 kOhm [CR0805-FX-6191ELF]	6.2 kOhm [4814P-1-622LF]	6.2 MOhm [CR0603-JW-625ELF]
6.04 kOhm [CR0402-FX-6041GLF]	6.19 kOhm [CR0805-FX-6191GLF]	6.2 kOhm [4816P-1-622]	6.2 MOhm [CR0805-FX-6204ELF]
6.04 kOhm [CR0603-FX-6041ELF]	6.19 kOhm [CR1206-FX-6191ELF]	6.2 kOhm [4816P-T02-622]	6.2 MOhm [CR0805-JW-625ELF]
6.04 kOhm [CR0805-FX-6041ELF]	6.19 kOhm [CRT0402-FZ-6191GLF]	6.2 kOhm [CAY16-622J4LF]	6.2 MOhm [CR1206-JW-625ELF]
6.04 kOhm [CR1206-FX-6041ELF]	6.19 kOhm [CRT0805-CX-6191ELF]	6.2 kOhm [CR0402-FX-6201GLF]	6.2 nF [C0603C622K3HACT U]
6.04 kOhm [CRT0603-BY-6041ELF]	6.2 kOhm [4114R-2-622]	6.2 kOhm [CR0402-JW-622GLF]	6.2 nF [C0603C622K5HACT U]
6.04 kOhm [CRT0805-FZ-6041ELF]	6.2 kOhm [4114R-2-622LF]	6.2 kOhm [CR0603-JW-622ELF]	6.2 nF [C0805C622K1GACT U]
6.04 Ohm [CRT0805-BY-6R04ELF]	6.2 kOhm [4116R-2-622]	6.2 kOhm [CR0805-FX-6201ELF]	6.2 nF [C0805C622K1HACT U]
6.1 uH [SRR1260-6R1Y]	6.2 kOhm [4309R-101-622]	6.2 kOhm [CR0805-JW-622ELF]	

Multisim 14.1 Education Components

6.2 nF [C0805C622K3HACT U]	6.2 Ohm [CRM2512-JW- 6R2ELF]	6.34 kOhm [CR0603-FX- 6341ELF]	6.65 kOhm [CR0402-FX- 6651GLF]
6.2 nF [C0805C622K5HACT U]	6.2 Ohm [FW10A6R20JA]	6.34 kOhm [CR0805-FX- 6341ELF]	6.65 kOhm [CR0603-FX- 6651ELF]
6.2 nF [C2225C622KBGAC TU]	6.2 Ohm [FW20A6R20JA]	6.34 kOhm [CR1206-FX- 6341ELF]	6.65 kOhm [CR0805-FX- 6651ELF]
6.2 Ohm [CR0402- J/-6R2GLF]	6.2 Ohm [PWR263S-20- 6R20FE]	6.34 kOhm [CRT0603-BW- 6341ELF]	6.65 kOhm [CR1206-FX- 6651ELF]
6.2 Ohm [CR0603- J/-6R2ELF]	6.2 uH [SDR7030- 6R2M]	6.34 kOhm [CRT0603-DV- 6341ELF]	6.8 kOhm [4108R- 1-682LF]
6.2 Ohm [CR0805- J/-6R2ELF]	6.2 uH [SRN6028- 6R2M]	6.49 kOhm [CR0402-FX- 6491GLF]	6.8 kOhm [4114R- 1-682]
6.2 Ohm [CR1206- J/-6R2ELF]	6.2 uH [SRR4011- 6R2YL]	6.49 kOhm [CR0603-FX- 6491ELF]	6.8 kOhm [4114R- 1-682LF]
6.2 Ohm [CRL0603- FW-6R20ELF]	6.2 uH [SRR5018- 6R2Y]	6.49 kOhm [CR0805-FX- 6491ELF]	6.8 kOhm [4114R- 2-682]
6.2 Ohm [CRL0603- JW-6R20ELF]	6.2 uH [SRR5028- 6R2Y]	6.49 kOhm [CR1206-FX- 6491ELF]	6.8 kOhm [4114R- 2-682LF]
6.2 Ohm [CRL0805- FW-6R20ELF]	6.2 uH [SRR6038- 6R2Y]	6.49 kOhm [CR0805-FX- 6491ELF]	6.8 kOhm [4116R- 1-682]
6.2 Ohm [CRL1206- FW-6R20ELF]	6.2 uH [SRU1038- 6R2Y]	6.49 kOhm [CR1206-FX- 6491ELF]	6.8 kOhm [4116R- 1-682LF]
6.2 Ohm [CRL2010- FW-6R20ELF]	6.2 uH [SRU1038A- 6R2Y]	6.49 kOhm [CRT0603-BY- 6491ELF]	6.8 kOhm [4116R- 2-682]
6.2 Ohm [CRL2010- JW-6R20ELF]	6.3 uH [SRR7045- 6R3M]	6.5 uH [SRR1208- 6R5ML]	6.8 kOhm [4116R- 2-682LF]
6.2 Ohm [CRL2512- FW-6R20ELF]	6.34 kOhm [CR0402-FX- 6341GLF]		6.8 kOhm [4304M- 101-682]

Multisim 14.1 Education Components

6.8 kOhm [4306M-101-682]	6.8 kOhm [4308R-102-682LF]	6.8 kOhm [4605X-101-682LF]	6.8 kOhm [4610M-101-682LF]
6.8 kOhm [4306M-101-682LF]	6.8 kOhm [4309R-101-682]	6.8 kOhm [4606X-101-682LF]	6.8 kOhm [4610X-101-682LF]
6.8 kOhm [4306R-101-682]	6.8 kOhm [4309R-101-682LF]	6.8 kOhm [4606X-102-682LF]	6.8 kOhm [4610X-102-682LF]
6.8 kOhm [4306R-101-682LF]	6.8 kOhm [4310H-101-682]	6.8 kOhm [4606X-AP2-682LF]	6.8 kOhm [4611X-101-682LF]
6.8 kOhm [4306R-102-682]	6.8 kOhm [4310H-101-682LF]	6.8 kOhm [4607X-101-682LF]	6.8 kOhm [4612X-102-682LF]
6.8 kOhm [4306R-102-682LF]	6.8 kOhm [4310H-102-682]	6.8 kOhm [4608M-102-682LF]	6.8 kOhm [4814P-2-682]
6.8 kOhm [4308H-102-682]	6.8 kOhm [4310H-102-682LF]	6.8 kOhm [4608X-101-682LF]	6.8 kOhm [4814P-2-682LF]
6.8 kOhm [4308H-102-682LF]	6.8 kOhm [4310M-101-682]	6.8 kOhm [4608X-102-682LF]	6.8 kOhm [4814P-T01-682]
6.8 kOhm [4308M-101-682]	6.8 kOhm [4310M-101-682LF]	6.8 kOhm [4608X-AP1-682LF]	6.8 kOhm [4814P-T01-682LF]
6.8 kOhm [4308M-101-682LF]	6.8 kOhm [4310R-101-682]	6.8 kOhm [4608X-AP2-682LF]	6.8 kOhm [4814P-T02-682]
6.8 kOhm [4308M-102-682]	6.8 kOhm [4310R-101-682LF]	6.8 kOhm [4609H-101-682LF]	6.8 kOhm [4814P-T02-682LF]
6.8 kOhm [4308M-102-682LF]	6.8 kOhm [4310R-102-682]	6.8 kOhm [4609M-101-682LF]	6.8 kOhm [4816P-1-682]
6.8 kOhm [4308R-101-682]	6.8 kOhm [4310R-102-682LF]	6.8 kOhm [4609X-101-682LF]	6.8 kOhm [4816P-1-682LF]
6.8 kOhm [4308R-101-682LF]	6.8 kOhm [4604X-101-682LF]	6.8 kOhm [4609X-AP1-682LF]	6.8 kOhm [4816P-2-682]
6.8 kOhm [4308R-102-682]	6.8 kOhm [4604X-102-682LF]	6.8 kOhm [4610H-101-682LF]	6.8 kOhm [4816P-2-682LF]

Multisim 14.1 Education Components

6.8 kOhm [4816P-T01-682]	6.8 kOhm [CAY10-682J4LF]	6.8 kOhm [CR1206-JW-682ELF]	6.8 kOhm [PWR4525W6801JE]
6.8 kOhm [4816P-T01-682LF]	6.8 kOhm [CAY16-6801F4LF]	6.8 kOhm [CR1206-JW-682GLF]	6.8 kOhm [PWR6327W6801J]
6.8 kOhm [4816P-T02-682]	6.8 kOhm [CAY16-682J4LF]	6.8 kOhm [CR2512-FX-6801ELF]	6.8 kOhm [PWR6327W6801JE]
6.8 kOhm [4816P-T02-682LF]	6.8 kOhm [CAY16-682J8LF]	6.8 kOhm [CR2512-JW-682ELF]	6.8 mH [SDR0503-682JL]
6.8 kOhm [4818P-2-682]	6.8 kOhm [CAY17-682JALF]	6.8 kOhm [CRM1206-FX-6801ELF]	6.8 mH [SDR0906-682KL]
6.8 kOhm [4818P-T02-682]	6.8 kOhm [CR0201-FW-6801GLF]	6.8 kOhm [CRM1206-JW-682ELF]	6.8 mH [SDR1005-682KL]
6.8 kOhm [4820P-1-682]	6.8 kOhm [CR0201-JW-682GLF]	6.8 kOhm [CRM2010-JW-682ELF]	6.8 mH [SRE6603-682M]
6.8 kOhm [4820P-2-682]	6.8 kOhm [CR0402-FX-6801GLF]	6.8 kOhm [CRM2512-FX-6801ELF]	6.8 mH [SRR0906-682YL]
6.8 kOhm [4820P-T02-682]	6.8 kOhm [CR0402-JW-682GLF]	6.8 kOhm [CRM2512-JW-682ELF]	6.8 mH [SRR0908-682YL]
6.8 kOhm [CAT10-682J4LF]	6.8 kOhm [CR0603-FX-6801ELF]	6.8 kOhm [CRM2512-JW-682ELF]	6.8 mH [SRR6603-682ML]
6.8 kOhm [CAT16-6801F4LF]	6.8 kOhm [CR0603-JW-682ELF]	6.8 kOhm [CRT0805-BY-6801ELF]	6.8 MOhm [4116R-1-685]
6.8 kOhm [CAT16-682J2LF]	6.8 kOhm [CR0603-JW-682GLF]	6.8 kOhm [CRT0805-DY-6801ELF]	6.8 MOhm [4116R-1-685LF]
6.8 kOhm [CAT16-682J4LF]	6.8 kOhm [CR0805-FX-6801ELF]	6.8 kOhm [PWR4525W6801J]	6.8 MOhm [CAT25-685JALF]
6.8 kOhm [CAT16-682J8LF]	6.8 kOhm [CR0805-JW-682ELF]		
6.8 kOhm [CAT25-682JALF]	6.8 kOhm [CR1206-FX-6801ELF]		

Multisim 14.1 Education Components

6.8 MOhm [CHV2512-JW-685ELF]	6.8 nF [C0603C682K3HACT U]	6.8 nF [C0805C682K3RACT U]	6.8 nF [C1206C682K5RACT U]
6.8 MOhm [CR0603-JW-685ELF]	6.8 nF [C0603C682K3RACT U]	6.8 nF [C0805C682K4RACT U]	6.8 nF [C1210C682K1GACT U]
6.8 MOhm [CR0805-JW-685ELF]	6.8 nF [C0603C682K4RACT U]	6.8 nF [C0805C682K5GACT U]	6.8 nF [C1210C682K1RACT U]
6.8 MOhm [CR1206-JW-685ELF]	6.8 nF [C0603C682K5HACT U]	6.8 nF [C0805C682K5HACT U]	6.8 nF [C1210C682K5GACT U]
6.8 nF [C0402C682K3RACT U]	6.8 nF [C0603C682K5RACT U]	6.8 nF [C0805C682K5RACT U]	6.8 nF [C1210C682K5RACT U]
6.8 nF [C0402C682K4RACT U]	6.8 nF [C0603C682K8RACT U]	6.8 nF [C1206C682K1HACT U]	6.8 nF [C1210C682KARACT U]
6.8 nF [C0402C682K5RACT U]	6.8 nF [C0805C682K1GACT U]	6.8 nF [C1206C682K1RACT U]	6.8 nF [C1812C682K1GACT U]
6.8 nF [C0402C682K8RACT U]	6.8 nF [C0805C682K1HACT U]	6.8 nF [C1206C682K3GACT U]	6.8 nF [C1812C682K1RACT U]
6.8 nF [C0603C682K1RACT U]	6.8 nF [C0805C682K1RACT U]	6.8 nF [C1206C682K3HACT U]	6.8 nF [C1812C682K5GACT U]
6.8 nF [C0603C682K2RACT U]	6.8 nF [C0805C682K3GACT U]	6.8 nF [C1206C682K3RACT U]	6.8 nF [C1812C682K5RACT U]
6.8 nF [C0603C682K3GACT U]	6.8 nF [C0805C682K3HACT U]	6.8 nF [C1206C682K5HACT U]	6.8 nF [C2220C682K2GACT U]

Multisim 14.1 Education Components

6.8 nF [C2225C682KBGAC TU]	6.8 nF [GPC7.3682K63K31 TR12]	6.8 nF [SPC10.2682K400A 31TR16]	6.8 Ohm [CRL0805- FW-6R80ELF]
6.8 nF [CDR06BP682BKSM]	6.8 nF [MMC5.7682K100J 31TR12]	6.8 nF [SPC10.2682K630A 31TR16]	6.8 Ohm [CRL0805- JW-6R80ELF]
6.8 nF [GMC5.7682K100J3 1TR12]	6.8 nF [MMC5.7682K250J 31TR12]	6.8 nF [SPC7.3682K100K31 TR12]	6.8 Ohm [CRL1206- FW-6R80ELF]
6.8 nF [GMC5.7682K250J3 1TR12]	6.8 nF [MMC5.7682K50J3 1TR12]	6.8 nF [SPC7.3682K250K33 TR12]	6.8 Ohm [CRL2010- FW-6R80ELF]
6.8 nF [GMC5.7682K50J31 TR12]	6.8 nF [MMC7.3682K100K 31TR12]	6.8 nF [SPC7.3682K400K37 TR12]	6.8 Ohm [CRL2010- JW-6R80ELF]
6.8 nF [GMC7.3682K100K3 1TR12]	6.8 nF [MMC7.3682K250K 31TR12]	6.8 Ohm [CR0402- J/-6R8GLF]	6.8 Ohm [CRM2512-FX- 6R80ELF]
6.8 nF [GMC7.3682K400K3 3TR12]	6.8 nF [MMC7.3682K400K 33TR12]	6.8 Ohm [CR0603- J/-6R8ELF]	6.8 Ohm [CRM2512-JW- 6R8ELF]
6.8 nF [GMC7.3682K63K31 TR12]	6.8 nF [MMC7.3682K50K3 1TR12]	6.8 Ohm [CR0805- J/-6R8ELF]	6.8 Ohm [FW10A6R80JA]
6.8 nF [GMC7.3683K100K3 5TR12]	6.8 nF [MMC7.3682K63K3 1TR12]	6.8 Ohm [CR1206- J/-6R8ELF]	6.8 Ohm [FW20A6R80JA]
6.8 nF [GPC7.3681K630K3 1TR12]	6.8 nF [SPC10.2682K100A 31TR16]	6.8 Ohm [CR2512- J/-6R8ELF]	6.8 Ohm [FW30A6R80JA]
6.8 nF [GPC7.3682K160K3 1TR12]	6.8 nF [SPC10.2682K250A 31TR16]	6.8 Ohm [CRL0603- FW-6R80ELF]	6.8 Ohm [FW50A6R80JA]
		6.8 Ohm [CRL0603- JW-6R80ELF]	6.8 Ohm [FW70A6R80JA]

Multisim 14.1 Education Components

6.8 Ohm [PWR2615W6R80F E]	6.8 uF [C1210C685K8PACT U]	6.8 uF [T429D685M006AH 4250]	6.8 uF [T491D685M035AT]
6.8 uF [A700V685M016AT E070]	6.8 uF [C1210C685M4VAC TU]	6.8 uF [T489B685M010AT E3K0]	6.8 uF [T491D685M050AT]
6.8 uF [C0805C685K8PACT U]	6.8 uF [MDC10685K100A5 7P7TUBE]	6.8 uF [T491A685M004AT]	6.8 uF [T491S685M004AT]
6.8 uF [C0805C685K9PACT U]	6.8 uF [MDC10685K100A5 7P8TUBE]	6.8 uF [T491A685M006AT]	6.8 uF [T491S685M006AT]
6.8 uF [C1206C685K4PACT U]	6.8 uF [MDC10685K50A55 P3TUBE]	6.8 uF [T491A685M010AT]	6.8 uF [T491S685M010AT]
6.8 uF [C1206C685K4PACT U]	6.8 uF [MDC10685K50A55 P3TUBE]	6.8 uF [T491A685M016AT]	6.8 uF [T491T685M010AT]
6.8 uF [C1206C685K4RACT U]	6.8 uF [MDC10685K50A55 P4TUBE]	6.8 uF [T491A685M020AT]	6.8 uF [T491U685M020AT]
6.8 uF [C1206C685K8RACT U]	6.8 uF [MDC10685K50A55 P5TUBE]	6.8 uF [T491B685M006AT]	6.8 uF [T491X685M050AT]
6.8 uF [C1206C685K9PACT U]	6.8 uF [MDC15685K50B53 P3TUBE]	6.8 uF [T491B685M010AT]	6.8 uF [T494A685M004AT]
6.8 uF [C1206C685K9PACT U]	6.8 uF [MMC16.5685K50C 31TR24]	6.8 uF [T491B685M016AT]	6.8 uF [T494A685M006AT]
6.8 uF [C1206C685K9RACT U]	6.8 uF [MMC16.5685K50C 31TR24]	6.8 uF [T491B685M025AT]	6.8 uF [T494A685M010AT]
6.8 uF [C1210C685K3PACT U]	6.8 uF [T419B685M006AH 4250]	6.8 uF [T491C685M016AT]	6.8 uF [T494A685M016AT]
6.8 uF [C1210C685K4PACT U]	6.8 uF [T419C685M010AH 4250]	6.8 uF [T491C685M020AT]	6.8 uF [T494A685M020AT]
		6.8 uF [T491C685M025AT]	6.8 uF [T494A685M020AT]
		6.8 uF [T491C685M035AT]	

Multisim 14.1 Education Components

6.8 uF [T494B685M010AT]	6.8 uF [T494U685M020AT]	6.8 uF [T498D685M035AT E900]	6.8 uF [TAJB685K010RNJ]
6.8 uF [T494B685M016AT]	6.8 uF [T494X685M050AT]	6.8 uF [T499C685M020AT E1K9]	6.8 uF [TAJB685K016RNJ]
6.8 uF [T494B685M020AT]	6.8 uF [T495C685M025AT E400]	6.8 uF [T521D685M050AT E090]	6.8 uF [TAJB685K020RNJ]
6.8 uF [T494B685M025AT]	6.8 uF [T495C685M025AT E500]	6.8 uF [T521V685M050AT E090]	6.8 uF [TAJC685K016RNJ]
6.8 uF [T494C685M016AT]	6.8 uF [T495D685M035AT E150]	6.8 uF [TACL685K002RTA]	6.8 uF [TAJC685K020RNJ]
6.8 uF [T494C685M020AT]	6.8 uF [T495D685M050AT E190]	6.8 uF [TACL685K003RTA]	6.8 uF [TAJC685K025RNJ]
6.8 uF [T494C685M025AT]	6.8 uF [T495D685M050AT E200]	6.8 uF [TACL685K004RTA]	6.8 uF [TAJC685K035RNJ]
6.8 uF [T494C685M035AT]	6.8 uF [T495D685M050AT E300]	6.8 uF [TACR685K006RTA]	6.8 uF [TAJD685K035RNJ]
6.8 uF [T494D685M035AT]	6.8 uF [T497B685M010AT 6110]	6.8 uF [TAJA685K006RNJ]	6.8 uF [TAJD685K050RNJ]
6.8 uF [T494D685M050AT]	6.8 uF [T498A685M016AT E2K6]	6.8 uF [TAJA685K010RNJ]	6.8 uF [TAJP685K010RNJ]
6.8 uF [T494S685M004AT]	6.8 uF [T498B685M016AT E1K8]	6.8 uF [TAJA685K016RNJ]	6.8 uF [TAJR685K002RNJ]
6.8 uF [T494S685M006AT]		6.8 uF [TAJA685K020RNJ]	6.8 uF [TAJR685K006RNJ]
6.8 uF [T494S685M010AT]		6.8 uF [TAJB685K006RNJ]	6.8 uF [TAJR685K010RNJ]
6.8 uF [T494T685M010AT]			

Multisim 14.1 Education Components

6.8 uF [TAJS685K004RNJ]	6.8 uF [TPSA685K016R150 0]	6.8 uF [TPSD685K050R060 0]	6.8 uH [SDR0906- 6R8ML]
6.8 uF [TAJS685K010RNJ]	6.8 uF [TPSB685K016R120 0]	6.8 uF [TPST685K010R180 0]	6.8 uH [SDR1005- 6R8ML]
6.8 uF [TAJT685K004RNJ]	6.8 uF [TPSB685K020R100 0]	6.8 uF [TRJA685K016RRJ]	6.8 uH [SDR1006- 6R8ML]
6.8 uF [TAJT685K006RNJ]	6.8 uF [TPSC685K020R070 0]	6.8 uF [TRJB685K025RRJ]	6.8 uH [SDR1030- 6R8M]
6.8 uF [TAJT685K010RNJ]	6.8 uF [TPSC685K025R050 0]	6.8 uF [TRJD685K050RRJ]	6.8 uH [SDR1045- 6R8M]
6.8 uF [TAJT685K016RNJ]	6.8 uF [TPSC685K025R060 0]	6.8 uH [SDE0403A- 6R8M]	6.8 uH [SDR1305- 6R8Y]
6.8 uF [TAJT685K020RNJ]	6.8 uF [TPSC685K025R070 0]	6.8 uH [SDE0604A- 6R8M]	6.8 uH [SDR1307- 6R8ML]
6.8 uF [TAJW685K025RNJ]	6.8 uF [TPSC685K025R040 0]	6.8 uH [SDE0805A- 6R8M]	6.8 uH [SDR1307A- 6R8M]
6.8 uF [THJA685K016RJN]	6.8 uF [TPSD685K035R015 0]	6.8 uH [SDE1006A- 6R8M]	6.8 uH [SDR6603- 6R8M]
6.8 uF [THJB685K016RJN]	6.8 uF [TPSD685K035R040 0]	6.8 uH [SDR0302- 6R8ML]	6.8 uH [SDR7045- 6R8M]
6.8 uF [THJC685K025RJN]	6.8 uF [TPSD685K035R050 0]	6.8 uH [SDR0403- 6R8ML]	6.8 uH [SRN3010- 6R8M]
6.8 uF [THJD685K035RJN]	6.8 uF [TPSD685K050R050 0]	6.8 uH [SDR0603- 6R8ML]	6.8 uH [SRN3015- 6R8M]
6.8 uF [TPSA685K006R180 0]	6.8 uF [TPSD685K050R060 0]	6.8 uH [SDR0604- 6R8ML]	6.8 uH [SRN4012T- 6R8M]
6.8 uF [TPSA685K010R180 0]	6.8 uF [TPSD685K050R070 0]	6.8 uH [SDR0703- 6R8ML]	6.8 uH [SRN4018- 6R8M]
		6.8 uH [SDR0805- 6R8ML]	6.8 uH [SRN4026- 6R8M]

Multisim 14.1 Education Components

6.8 uH [SRN5020-6R8M]	6.8 uH [SRP5015TA-6R8M]	6.8 uH [SRR1260A-6R8Y]	6.8 uH [SRU2011-6R8Y]
6.8 uH [SRN5040-6R8M]	6.8 uH [SRP5030T-6R8M]	6.8 uH [SRR1280-6R8Y]	6.8 uH [SRU2013-6R8Y]
6.8 uH [SRN6028-6R8M]	6.8 uH [SRP5030TA-6R8M]	6.8 uH [SRR3011-6R8YL]	6.8 uH [SRU3011-6R8Y]
6.8 uH [SRN6045-6R8Y]	6.8 uH [SRP6540-6R8M]	6.8 uH [SRR4018-6R8Y]	6.8 uH [SRU3014-6R8Y]
6.8 uH [SRN8040-6R8Y]	6.8 uH [SRP7028A-6R8M]	6.8 uH [SRR4028-6R8Y]	6.8 uH [SRU3017-6R8Y]
6.8 uH [SRP1038A-6R8M]	6.8 uH [SRP7030-6R8FM]	6.8 uH [SRR6040A-6R8Y]	6.8 uH [SRU5011-6R8Y]
6.8 uH [SRP1040-6R8M]	6.8 uH [SRR0603-6R8ML]	6.8 uH [SRR6603-6R8ML]	6.8 uH [SRU5016-6R8Y]
6.8 uH [SRP1235-6R8M]	6.8 uH [SRR0604-6R8ML]	6.8 uH [SRR7032-6R8M]	6.8 uH [SRU5018-6R8Y]
6.8 uH [SRP1245A-6R8M]	6.8 uH [SRR0618-6R8ML]	6.8 uH [SRR7045-6R8M]	6.8 uH [SRU5028-6R8Y]
6.8 uH [SRP1250-6R8M]	6.8 uH [SRR0906-6R8ML]	6.8 uH [SRU1028-6R8Y]	6.8 uH [SRU5028A-6R8Y]
6.8 uH [SRP1265A-6R8M]	6.8 uH [SRR1005-6R8M]	6.8 uH [SRU1028A-6R8Y]	6.8 uH [SRU6011-6R8Y]
6.8 uH [SRP1270-6R8M]	6.8 uH [SRR1210-6R8Y]	6.8 uH [SRU1038-6R8Y]	6.8 uH [SRU6018-6R8Y]
6.8 uH [SRP1770TA-6R8M]	6.8 uH [SRR1210A-6R8Y]	6.8 uH [SRU1048-6R8Y]	6.8 uH [SRU6025-6R8Y]
6.8 uH [SRP4012TA-6R8M]	6.8 uH [SRR1240-6R8M]	6.8 uH [SRU1048A-6R8Y]	6.8 uH [SRU6025A-6R8Y]
6.8 uH [SRP4020TA-6R8M]	6.8 uH [SRR1260-6R8Y]	6.8 uH [SRU2009-6R8Y]	6.8 uH [SRU8028-6R8Y]

Multisim 14.1 Education Components

6.8 uH [SRU8028A-6R8Y]	6.9 kOhm [4116R-1-692]	60.4 kOhm [CR0805-FX-6042ELF]	600 nH [SRP4012TA-R60M]
6.8 uH [SRU8043-6R8Y]	6.98 kOhm [CR0402-FX-6981GLF]	60.4 kOhm [CR1206-FX-6042ELF]	600 nH [SRP7050TA-R60M]
6.81 kOhm [CAT16-6811F4LF]	6.98 kOhm [CR0603-FX-6981ELF]	60.4 kOhm [CRT0805-BY-6042ELF]	604 kOhm [CAT16-6043F8LF]
6.81 kOhm [CR0402-FX-6811GLF]	6.98 kOhm [CR0805-FX-6981ELF]	60.4 Ohm [CAY16-60R4F4LF]	604 kOhm [CR0402-FX-6043GLF]
6.81 kOhm [CR0603-FX-6811ELF]	6.98 kOhm [CR1206-FX-6981ELF]	60.4 Ohm [CR0201-FW-60R4GLF]	604 kOhm [CR0603-FX-6043ELF]
6.81 kOhm [CR0805-FX-6811ELF]	6.98 kOhm [CRT0805-BY-6981ELF]	60.4 Ohm [CR0402-FX-60R4GLF]	604 kOhm [CR0805-FX-6043ELF]
6.81 kOhm [CR1206-FX-6811ELF]	60 mOhm [CRA2512-FZ-R060ELF]	60.4 Ohm [CR0603-FX-60R4ELF]	604 kOhm [CR1206-FX-6043ELF]
6.81 kOhm [CRT0402-FZ-6811GLF]	60 mOhm [CRA2512-JZ-R060ELF]	60.4 Ohm [CR0805-FX-60R4ELF]	604 kOhm [CRM2512-FX-6043ELF]
6.81 kOhm [CRT0603-BY-6811ELF]	60 mOhm [CRL0805-FW-R060ELF]	60.4 Ohm [CRM2512-FX-60R4ELF]	604 kOhm [CRT0805-BY-6043ELF]
6.81 kOhm [CRT0805-BY-6811ELF]	60.4 kOhm [CAT16-6042F8LF]	60.4 Ohm [CRT0805-BY-60R4ELF]	604 Ohm [CAY16-6040F4LF]
6.81 kOhm [CRT1206-FZ-6811ELF]	60.4 kOhm [CR0402-FX-6042GLF]	600 mOhm [PWR4318WR600F]	604 Ohm [CR0402-FX-6040GLF]
6.81 Ohm [CRM1206-FX-6R81ELF]	60.4 kOhm [CR0603-FX-6042ELF]	600 nH [SRP1235-R60M]	604 Ohm [CR0805-FX-6040ELF]

Multisim 14.1 Education Components

604 Ohm [CR1206-FX-6040ELF]	61.9 Ohm [CR0805-FX-61R9ELF]	619 Ohm [CR1206-FX-6190ELF]	62 kOhm [CR0805-JW-623ELF]
608PWM	61.9 Ohm [CR1206-FX-61R9ELF]	619 Ohm [CRT0402-FZ-6190GLF]	62 kOhm [CR1206-FX-6202ELF]
60LQ045	61.9 Ohm [CRT0402-FZ-61R9GLF]	62 kOhm [4114R-2-623]	62 kOhm [CR1206-JW-623ELF]
60LQ100	61.9 Ohm [CRT0805-FY-61R9ELF]	62 kOhm [4114R-2-623LF]	62 kOhm [CR2512-JW-623ELF]
61.9 kOhm [CR0201-FW-6192GLF]	61729-0010BLF	62 kOhm [4310R-102-623]	62 kOhm [CRT0603-FY-6202ELF]
61.9 kOhm [CR0402-FX-6192GLF]	619 kOhm [CR0402-FX-6193GLF]	62 kOhm [CAT16-6202F4LF]	62 kOhm [CRT0805-BW-6202ELF]
61.9 kOhm [CR0603-FX-6192ELF]	619 kOhm [CR0603-FX-6193ELF]	62 kOhm [CAY16-6202F4LF]	62 kOhm [CRT0805-CX-6202ELF]
61.9 kOhm [CR0805-FX-6192ELF]	619 kOhm [CR0805-FX-6193ELF]	62 kOhm [CAY16-623J4LF]	62 mF [C0805C629KBGAC TU]
61.9 kOhm [CR1206-FX-6192ELF]	619 kOhm [CR1206-FX-6193ELF]	62 kOhm [CR0201-FW-6202GLF]	62 mOhm [CRL1206-JW-R062ELF]
61.9 kOhm [CRT0603-BY-6192ELF]	619 Ohm [CR0402-FX-6190GLF]	62 kOhm [CR0402-FX-6202GLF]	62 mOhm [CRM2512-FX-R062ELF]
61.9 kOhm [CRT0805-CX-6192ELF]	619 Ohm [CR0603-FX-6190ELF]	62 kOhm [CR0402-JW-623GLF]	62 Ohm [4116R-1-620]
61.9 Ohm [CAT16-61R9F8LF]	619 Ohm [CR0805-FX-6190ELF]	62 kOhm [CR0603-FX-6202ELF]	62 Ohm [4116R-1-620LF]
61.9 Ohm [CR0402-FX-61R9GLF]	619 Ohm [CR0805-FX-6190GLF]	62 kOhm [CR0805-FX-6202ELF]	
61.9 Ohm [CR0603-FX-61R9ELF]			

Multisim 14.1 Education Components

62 Ohm [4308R-102-620]	62 Ohm [CR0603-JW-620ELF]	62 pF [C0603C620K5GACTU]	620 kOhm [CR0603-FX-6203ELF]
62 Ohm [4310M-102-620]	62 Ohm [CR0805-FX-62R0ELF]	62 pF [C0805C620KBGAC TU]	620 kOhm [CR0603-JW-624ELF]
62 Ohm [4310M-102-620LF]	62 Ohm [CR0805-FX-62R0GLF]	62 pF [C1206C620KBGAC TU]	620 kOhm [CR0805-FX-6203ELF]
62 Ohm [4605X-101-620LF]	62 Ohm [CR0805-JW-620ELF]	62 pF [C1206C620KDGAC TU]	620 kOhm [CR0805-JW-624ELF]
62 Ohm [4816P-1-620]	62 Ohm [CR1206-FX-62R0ELF]	62 pF [C1210C620KBGAC TU]	620 kOhm [CR1206-FX-6203ELF]
62 Ohm [4816P-1-620LF]	62 Ohm [CR1206-JW-620ELF]	62 pF [C1812C620KBGAC TU]	620 kOhm [CR1206-JW-624ELF]
62 Ohm [CAT10-620J4LF]	62 Ohm [CR2010-FX-62R0ELF]	62 pF [C1825C620KBGAC TU]	620 kOhm [CR2010-JW-624ELF]
62 Ohm [CAT16-620J4LF]	62 Ohm [CR2512-FX-62R0ELF]	62 pF [C2220C620KBGAC TU]	620 mOhm [CRL0603-FW-R620ELF]
62 Ohm [CAY10-620J2LF]	62 Ohm [CR2512-JW-620ELF]	62 pF [C2225C620KBGAC TU]	620 mOhm [CRL0603-JW-R620ELF]
62 Ohm [CAY10-620J4LF]	62 Ohm [CRM0805-JW-620ELF]	620 kOhm [CAY16-624J4LF]	620 mOhm [CRL0805-FW-R620ELF]
62 Ohm [CAY16-620J4LF]	62 Ohm [CRT0805-BW-62R0ELF]	620 kOhm [CR0402-FX-6203GLF]	620 mOhm [CRL0805-JW-R620ELF]
62 Ohm [CAY17-620JALF]	62 pF [C0402C620K3GACTU]		
62 Ohm [CR0402-FX-62R0GLF]	62 pF [C0402C620K5GACTU]		
62 Ohm [CR0402-JW-620GLF]			
62 Ohm [CR0603-FX-62R0ELF]			

Multisim 14.1 Education Components

620 mOhm [CRL1206-FW- R620ELF]	620 Ohm [4816P- T01-621LF]	620 pF [C0402C621K3HACT U]	620 pF [C2225C621KBGAC TU]
620 mOhm [CRL1206-JW- R620ELF]	620 Ohm [4816P- T02-621]	620 pF [C0402C621K5HACT U]	63.4 kOhm [CR0402-FX- 6342GLF]
620 mOhm [CRL2010-FW- R620ELF]	620 Ohm [CAY16- 621J4LF]	620 pF [C0603C621K1HACT U]	63.4 kOhm [CR0603-FX- 6342ELF]
620 mOhm [CRL2010-JW- R620ELF]	620 Ohm [CR0402- JW-621GLF]	620 pF [C0603C621K3HACT U]	63.4 kOhm [CR0805-FX- 6342ELF]
620 mOhm [CRL2512-JW- R620ELF]	620 Ohm [CR0603- FX-6200ELF]	620 pF [C0603C621K5GACT U]	63.4 kOhm [CR1206-FX- 6342ELF]
620 Ohm [4114R-2- 621]	620 Ohm [CR0805- FX-6200ELF]	620 pF [C0603C621K5HACT U]	63.4 kOhm [CRT0603-PW- 6342ELF]
620 Ohm [4605X- 101-621LF]	620 Ohm [CR0805- FX-6200GLF]	620 pF [C0805C621K5GACT U]	63.4 Ohm [CR0402- FX-63R4GLF]
620 Ohm [4606X- 101-621LF]	620 Ohm [CR0805- JW-621ELF]	620 pF [C1210C621KBGAC TU]	63.4 Ohm [CR0603- FX-63R4ELF]
620 Ohm [4609X- 101-621LF]	620 Ohm [CR1206- FX-6200ELF]	620 pF [C1812C621KBGAC TU]	63.4 Ohm [CR0805- FX-63R4ELF]
620 Ohm [4816P-1- 621]	620 Ohm [CR1206- JW-621ELF]	620 pF [C1825C621KBGAC TU]	63.4 Ohm [CR1206- FX-63R4ELF]
620 Ohm [4816P-1- 621LF]	620 Ohm [CR2512- JW-621ELF]	620 pF [C1825C621KBGAC TU]	634 kOhm [CR0402-FX- 6343GLF]
620 Ohm [4816P-2- 621]	620 Ohm [PWR3014W6200JE]	620 pF [C2220C621KBGAC TU]	634 kOhm [CR0603-FX- 6343ELF]
620 Ohm [4816P- T01-621]	620 pF [C0402C621K1HACT U]		

Multisim 14.1 Education Components

634 kOhm [CR0805-FX- 6343ELF]	64.9 kOhm [CRT0603-PW- 6492ELF]	649 Ohm [CR0402- FX-6490GLF]	66.5 Ohm [CR0603- FX-66R5ELF]
634 kOhm [CR1206-FX- 6343ELF]	64.9 Ohm [CR0603- FX-64R9ELF]	649 Ohm [CR0603- FX-6490ELF]	66.5 Ohm [CR0805- FX-66R5ELF]
634 Ohm [CR0402- FX-6340GLF]	64.9 Ohm [CR0805- FX-64R9ELF]	649 Ohm [CR0805- FX-6490ELF]	66.5 Ohm [CR1206- FX-66R5ELF]
634 Ohm [CR0603- FX-6340ELF]	64.9 Ohm [CR1206- FX-64R9ELF]	649 Ohm [CR1206- FX-6490ELF]	66.5 Ohm [CR2010- FX-66R5ELF]
634 Ohm [CR0805- FX-6340ELF]	64.9 Ohm [CRT0805-FY- 64R9ELF]	649 Ohm [CRT0402-FZ- 6490GLF]	66.5 Ohm [CRT0402-BY- 66R5GLF]
634 Ohm [CR1206- FX-6340ELF]	640455-5 640455-8	649 Ohm [CRT0603-PV- 6490ELF]	662 kOhm [CR0402-FX- 6623GLF]
64.9 kOhm [CR0201-FW- 6492GLF]	649 kOhm [CR0402-FX- 6493GLF]	649 Ohm [CRT0805-DZ- 6490ELF]	665 kOhm [CR0402-FX- 6653GLF]
64.9 kOhm [CR0402-FX- 6492GLF]	649 kOhm [CR0603-FX- 6493ELF]	65 mOhm [CRA2512-JZ- R065ELF]	665 kOhm [CR0603-FX- 6653ELF]
64.9 kOhm [CR0603-FX- 6492ELF]	649 kOhm [CR0805-FX- 6493ELF]	66.5 kOhm [CR0402-FX- 6652GLF]	665 kOhm [CR0805-FX- 6653ELF]
64.9 kOhm [CR0805-FX- 6492ELF]	649 kOhm [CR1206-FX- 6493ELF]	66.5 kOhm [CR0603-FX- 6652ELF]	665 kOhm [CR1206-FX- 6653ELF]
64.9 kOhm [CR1206-FX- 6492ELF]	649 kOhm [CR2010-FX- 6493ELF]	66.5 kOhm [CR0805-FX- 6652ELF]	665 Ohm [CR0402- FX-6650GLF]
64.9 kOhm [CRT0603-DZ- 6492ELF]	649 Ohm [CAT16- 6490F8LF]	66.5 kOhm [CR1206-FX- 6652ELF]	665 Ohm [CR0603- FX-6650ELF]
			665 Ohm [CR0805- FX-6650ELF]

Multisim 14.1 Education Components

665 Ohm [CR1206-FX-6650ELF]	68 kOhm [4306R-102-683LF]	68 kOhm [4420P-2-683]	68 kOhm [4610X-102-683LF]
665 Ohm [CRT0805-BY-6650ELF]	68 kOhm [4308H-102-683LF]	68 kOhm [4420P-T01-683]	68 kOhm [4814P-1-683]
665 Ohm [CRT1206-BY-6650ELF]	68 kOhm [4308R-101-683]	68 kOhm [4420P-T02-683]	68 kOhm [4814P-1-683LF]
670 nH [SRP1235-R67M]	68 kOhm [4308R-102-683]	68 kOhm [4604X-102-683LF]	68 kOhm [4814P-T01-683]
68 kOhm [4114R-1-683]	68 kOhm [4308R-102-683LF]	68 kOhm [4605X-101-683LF]	68 kOhm [4814P-T01-683LF]
68 kOhm [4114R-1-683LF]	68 kOhm [4308R-101-683]	68 kOhm [4606X-101-683LF]	68 kOhm [4814P-T02-683]
68 kOhm [4114R-2-683]	68 kOhm [4310H-101-683]	68 kOhm [4606X-102-683LF]	68 kOhm [4814P-T02-683LF]
68 kOhm [4114R-2-683LF]	68 kOhm [4310H-101-683LF]	68 kOhm [4607X-101-683LF]	68 kOhm [4816P-1-683]
68 kOhm [4116R-1-683]	68 kOhm [4310R-101-683]	68 kOhm [4608X-101-683LF]	68 kOhm [4816P-1-683LF]
68 kOhm [4116R-1-683LF]	68 kOhm [4310R-101-683LF]	68 kOhm [4608X-102-683LF]	68 kOhm [4816P-2-683]
68 kOhm [4116R-2-683]	68 kOhm [4310R-102-683]	68 kOhm [4609H-101-683LF]	68 kOhm [4816P-2-683LF]
68 kOhm [4116R-2-683LF]	68 kOhm [4310R-102-683LF]	68 kOhm [4609X-101-683LF]	68 kOhm [4816P-T01-683]
68 kOhm [4306R-101-683]	68 kOhm [4416P-2-683]	68 kOhm [4610H-101-683LF]	68 kOhm [4816P-T01-683LF]
68 kOhm [4306R-101-683LF]	68 kOhm [4416P-T02-683]	68 kOhm [4610H-102-683LF]	68 kOhm [4816P-T02-683]
68 kOhm [4306R-102-683]	68 kOhm [4420P-1-683]	68 kOhm [4610X-101-683LF]	68 kOhm [4816P-T02-683LF]

Multisim 14.1 Education Components

68 kOhm [4818P-T01-683]	68 kOhm [CR0805-FX-6802ELF]	68 nF [05083C683KAT2A]	68 nF [C0603C683K9RACTU]
68 kOhm [CAT10-683J4LF]	68 kOhm [CR0805-FX-6802GLF]	68 nF [0508ZC683KAT2S]	68 nF [C0603C683M3VACTU]
68 kOhm [CAT16-6802F4LF]	68 kOhm [CR0805-JW-683ELF]	68 nF [06125C683KAT2W]	68 nF [C0805C683K1RACTU]
68 kOhm [CAT16-683J4LF]	68 kOhm [CR0805-JW-683GLF]	68 nF [C0402C683K4RACTU]	68 nF [C0805C683K3RACTU]
68 kOhm [CAT25-683JALF]	68 kOhm [CR1206-FX-6802ELF]	68 nF [C0402C683K8PACTU]	68 nF [C0805C683K4RACTU]
68 kOhm [CAY10-683J4LF]	68 kOhm [CR1206-JW-683ELF]	68 nF [C0402C683K8PACTU]	68 nF [C0805C683K5RACTU]
68 kOhm [CAY16-6802F4LF]	68 kOhm [CR2010-JW-683ELF]	68 nF [C0402C683K8PACTU]	68 nF [C0805C683K8PACTU]
68 kOhm [CAY16-683J4LF]	68 kOhm [CR2512-JW-683ELF]	68 nF [C0402C683K9PACTU]	68 nF [C0805C683K8PACTU]
68 kOhm [CAY16-683J8LF]	68 kOhm [CRM2512-JW-683ELF]	68 nF [C0402C683K9PACTU]	68 nF [C0805C683M5UACTU]
68 kOhm [CAY17-683JALF]	68 mF [C0402C689K8GACTU]	68 nF [C0603C683K3RACTU]	68 nF [C0805F683K3RACTU]
68 kOhm [CR0201-FW-6802GLF]	68 mF [C1206C689K2GACTU]	68 nF [C0603C683K4RACTU]	68 nF [C0805F683K4RACTU]
68 kOhm [CR0402-FX-6802GLF]	68 mF [C1206C689K2GACTU]	68 nF [C0603C683K5RACTU]	68 nF [C0805F683K5RACTU]
68 kOhm [CR0402-JW-683GLF]	68 nF [0306YC683KAT2A]	68 nF [C0603C683K8RACTU]	
68 kOhm [CR0603-FX-6802ELF]	68 nF [0306ZC683KAT2A]		
68 kOhm [CR0603-JW-683ELF]			

Multisim 14.1 Education Components

68 nF [C1206C683K1RACT U]	68 nF [C1206F683K5RACT U]	68 nF [C1210F683K2RACT U]	68 nF [CA064C683K4RACT U]
68 nF [C1206C683K2RACT U]	68 nF [C1210C683K1GACT U]	68 nF [C1812C683K1GACT U]	68 nF [CDR05BX683BKSM]
68 nF [C1206C683K3GACT U]	68 nF [C1210C683K1HACT U]	68 nF [C1812C683K1HACT U]	68 nF [GMC5.7683K50J31 TR12]
68 nF [C1206C683K3HACT U]	68 nF [C1210C683K1RACT U]	68 nF [C1812C683K1RACT U]	68 nF [GMC7.3682K250K3 1TR12]
68 nF [C1206C683K5HACT U]	68 nF [C1210C683K2RACT U]	68 nF [C1812C683K2RACT U]	68 nF [GMC7.3683K63K31 TR12]
68 nF [C1206C683K5RACT U]	68 nF [C1210C683K3GACT U]	68 nF [C1812C683K5GACT U]	68 nF [GPC7.3683K63K35 TR12]
68 nF [C1206C683KARACT U]	68 nF [C1210C683K3HACT U]	68 nF [C1812C683K5HACT U]	68 nF [MDC10683K100A5 2P3TUBE]
68 nF [C1206C683M5UAC TU]	68 nF [C1210C683K5GACT U]	68 nF [C1812C683K5RACT U]	68 nF [MDC10683K250A5 2P3TUBE]
68 nF [C1206F683K1RACT U]	68 nF [C1210C683K5HACT U]	68 nF [C2220C683K1GACT U]	68 nF [MDC10683K400A5 2P3TUBE]
68 nF [C1206F683K3RACT U]	68 nF [C1210C683K5RACT U]	68 nF [C2220C683K2GACT U]	68 nF [MDC10683K50A52 P3TUBE]
68 nF [C1206F683K4RACT U]	68 nF [C1210C683KARACT U]	68 nF [C2220C683K5GACT U]	68 nF [MDC10683K630A5 4P3TUBE]

Multisim 14.1 Education Components

68 nF [MDC10683K630A5 4P4TUBE]	68 nF [MDS10683K250A5 2P3TUBE]	68 nF [SPC12.7683K250B 31TR24]	68 Ohm [4306M- 101-680]
68 nF [MDC15683K100B5 3P3TUBE]	68 nF [MDS10683K400A5 2P3TUBE]	68 nF [SPC16.5683K400C 31TR24]	68 Ohm [4306M- 101-680LF]
68 nF [MDC15683K250B5 3P3TUBE]	68 nF [MDS10683K50A52 P3TUBE]	68 nF [SPC16.5683K630C 31TR24]	68 Ohm [4306R- 101-680]
68 nF [MDC15683K400B5 3P3TUBE]	68 nF [MDS15683K100B5 3P3TUBE]	68 nF [W2L1YC683MAT1A]	68 Ohm [4306R- 102-680]
68 nF [MDC15683K50B53 P3TUBE]	68 nF [MDS15683K250B5 3P3TUBE]	68 nF [W2L1YC683MAT1S]	68 Ohm [4306R- 102-680LF]
68 nF [MDC15683K630B5 3P3TUBE]	68 nF [MDS15683K400B5 3P3TUBE]	68 Ohm [4114R-1- 680]	68 Ohm [4308H- 102-680LF]
68 nF [MDK10683K100A5 2P3TUBE]	68 nF [MDS15683K630B5 3P3TUBE]	68 Ohm [4114R-1- 680LF]	68 Ohm [4308M- 101-680]
68 nF [MDK10683K250A5 2P3TUBE]	68 nF [MMC5.7683K50J3 1TR12]	68 Ohm [4114R-2- 680]	68 Ohm [4308M- 101-680LF]
68 nF [MDK10683K400A5 2P3TUBE]	68 nF [MMC7.3683K100K 31TR12]	68 Ohm [4114R-2- 680LF]	68 Ohm [4308M- 102-680]
68 nF [MDK10683K50A52 P3TUBE]	68 nF [MMC7.3683K50K3 1TR12]	68 Ohm [4116R-1- 680]	68 Ohm [4308R- 101-680]
68 nF [MDS10683K100A5 2P3TUBE]	68 nF [SPC10.2683K100A 31TR16]	68 Ohm [4116R-1- 680LF]	68 Ohm [4308R- 101-680LF]
		68 Ohm [4116R-2- 680]	68 Ohm [4308R- 102-680]
		68 Ohm [4116R-2- 680LF]	68 Ohm [4308R- 102-680LF]

Multisim 14.1 Education Components

68 Ohm [4309R-101-680]	68 Ohm [4604X-102-680LF]	68 Ohm [4814P-T01-680]	68 Ohm [CAT25-680JALF]
68 Ohm [4310M-101-680]	68 Ohm [4605X-101-680LF]	68 Ohm [4814P-T01-680LF]	68 Ohm [CAY10-680J4LF]
68 Ohm [4310M-102-680]	68 Ohm [4606X-101-680LF]	68 Ohm [4814P-T02-680]	68 Ohm [CAY16-680J4GLF]
68 Ohm [4310M-102-680LF]	68 Ohm [4606X-102-680LF]	68 Ohm [4816P-1-680]	68 Ohm [CAY16-680J4LF]
68 Ohm [4310R-101-680]	68 Ohm [4607X-101-680LF]	68 Ohm [4816P-1-680LF]	68 Ohm [CAY16-680J8LF]
68 Ohm [4310R-101-680LF]	68 Ohm [4608H-102-680LF]	68 Ohm [4816P-2-680]	68 Ohm [CAY16-68R0F4LF]
68 Ohm [4310R-102-680]	68 Ohm [4608X-101-680LF]	68 Ohm [4816P-2-680LF]	68 Ohm [CAY17-680JALF]
68 Ohm [4310R-102-680LF]	68 Ohm [4608X-102-680LF]	68 Ohm [4816P-T01-680]	68 Ohm [CR0402-FX-68R0GLF]
68 Ohm [4416P-1-680]	68 Ohm [4608X-AP2-680LF]	68 Ohm [4816P-T01-680LF]	68 Ohm [CR0402-JW-680GLF]
68 Ohm [4416P-2-680]	68 Ohm [4609X-101-680LF]	68 Ohm [4816P-T02-680]	68 Ohm [CR0603-FX-68R0ELF]
68 Ohm [4420P-1-680]	68 Ohm [4610X-101-680LF]	68 Ohm [4816P-T02-680LF]	68 Ohm [CR0603-JW-680ELF]
68 Ohm [4420P-2-680]	68 Ohm [4610X-102-680LF]	68 Ohm [CAT10-680J4LF]	68 Ohm [CR0603-JW-680GLF]
68 Ohm [4420P-T01-680]	68 Ohm [4612X-102-680LF]	68 Ohm [CAT16-680J4LF]	68 Ohm [CR0805-FX-68R0ELF]
68 Ohm [4420P-T02-680]	68 Ohm [4614X-102-680LF]	68 Ohm [CAT16-680J8LF]	68 Ohm [CR0805-JW-680ELF]
68 Ohm [4604X-101-680LF]	68 Ohm [4814P-1-680]	68 Ohm [CAT16-68R0F4LF]	68 Ohm [CR1206-FX-68R0ELF]

Multisim 14.1 Education Components

68 Ohm [CR1206-JW-680ELF]	68 Ohm [PWR4525W68R0JE]	68 pF [C0603C680K5GACT U]	68 pF [C1210C680KBGAC TU]
68 Ohm [CR1206-JW-680GLF]	68 Ohm [PWR6327N68R0FE]	68 pF [C0805C680K1GACT U]	68 pF [C1812C680KBGAC TU]
68 Ohm [CR2010-JW-680ELF]	68 Ohm [PWR6327W68R0J]	68 pF [C0805C680K2GACT U]	68 pF [C1825C680KBGAC TU]
68 Ohm [CRM1206-FX-68R0ELF]	68 Ohm [PWR6327W68R0JE]	68 pF [C0805C680K5GACT U]	68 pF [C2220C680KBGAC TU]
68 Ohm [CRM2512-JW-680ELF]	68 Ohm [WS2M68R0J]	68 pF [C0805C680KBGAC TU]	68 pF [C2225C680KBGAC TU]
68 Ohm [FW10A68R0JA]	68 pF [C0201C680K3GACT U]	68 pF [C1206C680K1GACT U]	68 pF [CA064C680K5GAC TU]
68 Ohm [FW20A68R0JA]	68 pF [C0402C680K3GACT U]	68 pF [C1206C680K2GACT U]	68 pF [CA064C680K8GAC TU]
68 Ohm [FW30A68R0JA]	68 pF [C0402C680K5GACT U]	68 pF [C1206C680K5GACT U]	68 pF [CDR01BP680BKSM]]
68 Ohm [FW50A68R0JA]	68 pF [C0402C680K8GACT U]	68 pF [C1206C680KBGAC TU]	68 uF [10SVPC68MV]
68 Ohm [FW70A68R0JA]	68 pF [C0603C680K2GACT U]	68 pF [C1206C680KDGAC TU]	68 uF [10TPC68M]
68 Ohm [PWR2615W68R0J]	68 pF [C0603C680K3GACT U]	68 pF [C1206C680KGGAC TU]	68 uF [16SVPC68M]
68 Ohm [PWR2615W68R0JE]]	68 pF [C0603C680K4GACT U]		68 uF [16TQC68MYF]

Multisim 14.1 Education Components

68 uF [20SVP68M]	68 uF [EEFCX1A680R]	68 uF [T491B686M006AT]	68 uF [T491U686M006AT]
68 uF [4TPB68M]]
68 uF [4TPH68MHA]	68 uF [EEFCX1C680R]	68 uF [T491B686M010AT]	68 uF [T491U686M010AT]
68 uF [4TPU68MSI]	68 uF [EEFHX1A680R]	68 uF [T491C686M004AT]]
68 uF [6TPB68M]	68 uF [EEFHX1C680R]	68 uF [T491C686M006AT]	68 uF [T491V686M010AT]
68 uF [A700D686M008AT E015]	68 uF [EEFLR0J680R]	68 uF [T491C686M010AT]	68 uF [T491V686M016AT]
68 uF [A700D686M008AT E018]	68 uF [EEFSR0J680R]	68 uF [T491C686M016AT]	68 uF [T491X686M020AT]
68 uF [A700D686M010AT E015]	68 uF [EEHZA1H680P]	68 uF [T491D686M004AT]	68 uF [T491X686M025AT]
68 uF [A700D686M010AT E018]	68 uF [EEHZA1V680XP]	68 uF [T491D686M006AT]	68 uF [T494A686M004AT]
68 uF [A700V686M006AT E018]	68 uF [EEHZC1H680P]	68 uF [T491D686M010AT]	68 uF [T494B686M004AT]
68 uF [A700V686M006AT E018]	68 uF [LDEDD3680KA5N00]	68 uF [T491D686M016AT]	68 uF [T494B686M006AT]
68 uF [A700V686M006AT E025]	68 uF [T419G686M010AH 4250]	68 uF [T491D686M020AT]	68 uF [T494B686M010AT]
68 uF [A700V686M006AT E028]	68 uF [T491A686M004AT]	68 uF [T491D686M025AT]	68 uF [T494C686M004AT]
68 uF [EEFCS0J680R]	68 uF [T491A686M006AT]	68 uF [T491U686M004AT]	68 uF [T494C686M010AT]
68 uF [EEFCT1A680R]	68 uF [T491B686M004AT]		68 uF [T494C686M016AT]

Multisim 14.1 Education Components

68 uF [T494D686M004AT]	68 uF [T494X686M025AT]	68 uF [T495D686M020AT E150]	68 uF [T520A686M006AT E150]
68 uF [T494D686M006AT]	68 uF [T495B686M010AT E900]	68 uF [T495D686M025AT E150]	68 uF [T520A686M2R5AT E070]
68 uF [T494D686M010AT]	68 uF [T495C686M010AT E225]	68 uF [T495D686M025AT E200]	68 uF [T520A686M2R5AT E080]
68 uF [T494D686M016AT]	68 uF [T495D686M006AT E175]	68 uF [T495V686M010AT E100]	68 uF [T520B686M004AT E025]
68 uF [T494D686M020AT]	68 uF [T495D686M010AT E070]	68 uF [T495V686M010AT E140]	68 uF [T520B686M004AT E035]
68 uF [T494D686M025AT]	68 uF [T495D686M010AT E090]	68 uF [T495V686M016AT E300]	68 uF [T520B686M004AT E040]
68 uF [T494U686M004AT]	68 uF [T495D686M010AT E150]	68 uF [T495X686M010AT E150]	68 uF [T520B686M004AT E070]
68 uF [T494U686M006AT]	68 uF [T495D686M016AT E070]	68 uF [T495X686M020AT E150]	68 uF [T520B686M006AT E025]
68 uF [T494U686M010AT]	68 uF [T495D686M016AT E100]	68 uF [T495X686M025AT E125]	68 uF [T520B686M006AT E035]
68 uF [T494V686M010AT]	68 uF [T495D686M016AT E150]	68 uF [T495X686M025AT E200]	68 uF [T520B686M006AT E040]
68 uF [T494V686M016AT]	68 uF [T495D686M020AT E070]	68 uF [T513X686M025AH 6110]	68 uF [T520B686M006AT E070]
68 uF [T494X686M020AT]			

Multisim 14.1 Education Components

68 uF [T520C686M006AT E100]	68 uF [T520V686M010AT E060]	68 uF [TAJB686K006RNJ]	68 uF [TAJX686K016RNJ]
68 uF [T520C686M010AT E045]	68 uF [T520V686M010AT E100]	68 uF [TAJB686K010RNJ]	68 uF [TAJY686K010RNJ]
68 uF [T520T686M004AT E070]	68 uF [T520W686M010AT E040]	68 uF [TAJC686K006RNJ]	68 uF [TAJY686K016RNJ]
68 uF [T520T686M006AT E070]	68 uF [T521D686M016AT E050]	68 uF [TAJC686K016RNJ]	68 uF [THJC686K006RJJ]
68 uF [T520T686M006AT E150]	68 uF [T521V686M016AT E050]	68 uF [TAJD686K006RNJ]	68 uF [THJD686K016RJJ]
68 uF [T520U686M004AT E055]	68 uF [T521V686M016AT E090]	68 uF [TAJD686K016RNJ]	68 uF [TPMD686K016R00 50]
68 uF [T520U686M006AT E055]	68 uF [T525B686M004AT E080]	68 uF [TAJD686K020RNJ]	68 uF [TPME686K025R00 45]
68 uF [T520U686M006AT E070]	68 uF [T525B686M006AT E080]	68 uF [TAJE686K020RNJ]	68 uF [TPME686K025R00 55]
68 uF [T520V686M010AT E025]	68 uF [T525T686M004AT E080]	68 uF [TAJT686K004RNJ]	68 uF [TPSB686K006R035 0]
68 uF [T520V686M010AT E040]	68 uF [T543U686M006AT E055]	68 uF [TAJV686K025RNJ]	68 uF [TPSB686K006R050 0]
68 uF [T520V686M010AT E045]	68 uF [TAJA686K002RNJ]	68 uF [TAJW686K006RNJ]	68 uF [TPSC686K006R015 0]
	68 uF [TAJB686K004RNJ]	68 uF [TAJW686K010RNJ]	68 uF [TPSC686K006R020 0]

Multisim 14.1 Education Components

68 uF [TPSC686K010R020 0]	68 uF [TPSD686K020R030 0]	68 uF [TPSW686K006R02 50]	68 uH [SDR0302- 680KL]
68 uF [TPSC686K010R030 0]	68 uF [TPSE686K020R012 5]	68 uF [TPSW686K010R01 00]	68 uH [SDR0403- 680KL]
68 uF [TPSC686K016R020 0]	68 uF [TPSE686K020R015 0]	68 uF [TPSY686K010R010 0]	68 uH [SDR0503- 680KL]
68 uF [TPSD686K010R010 0]	68 uF [TPSE686K020R020 0]	68 uF [TPSY686K010R020 0]	68 uH [SDR0604- 680KL]
68 uF [TPSD686K010R015 0]	68 uF [TPSE686K025R012 5]	68 uF [TPSY686K016R020 0]	68 uH [SDR0703- 680KL]
68 uF [TPSD686K016R007 0]	68 uF [TPSE686K025R020 0]	68 uF [TPSY686K016R025 0]	68 uH [SDR0906- 680KL]
68 uF [TPSD686K016R010 0]	68 uF [TPSV686K025R008 0]	68 uF [TRJC686K010RRJ]	68 uH [SDR1005- 680KL]
68 uF [TPSD686K016R015 0]	68 uF [TPSV686K025R009 5]	68 uF [TRJD686K020RRJ]	68 uH [SDR1006- 680KL]
68 uF [TPSD686K020R007 0]	68 uF [TPSV686K025R015 0]	68 uF [TRJE686K020RRJ]	68 uH [SDR1030- 680M]
68 uF [TPSD686K020R015 0]	68 uF [TPSV686K025R020 0]	68 uH [SDE0403A- 680K]	68 uH [SDR1045- 680M]
68 uF [TPSD686K020R020 0]	68 uF [TPSW686K006R01 25]	68 uH [SDE0604A- 680K]	68 uH [SDR1105- 680KL]
		68 uH [SDE0805A- 680K]	68 uH [SDR1305- 680M]
		68 uH [SDE1006A- 680K]	68 uH [SDR1307- 680KL]

Multisim 14.1 Education Components

68 uH [SDR1307A-680K]	68 uH [SRR0735A-680M]	68 uH [SRR1260-680M]	68 uH [SRR7045-680M]
68 uH [SDR1806-680ML]	68 uH [SRR0745A-680M]	68 uH [SRR1260A-680M]	68 uH [SRU1028-680Y]
68 uH [SDR6603-680M]	68 uH [SRR0804-680K]	68 uH [SRR1280-680M]	68 uH [SRU1028A-680Y]
68 uH [SDR7030-680K]	68 uH [SRR0805-680K]	68 uH [SRR1806-680M]	68 uH [SRU1038-680Y]
68 uH [SDR7045-680K]	68 uH [SRR0905-680Y]	68 uH [SRR3011-680YL]	68 uH [SRU1038A-680Y]
68 uH [SRN4018-680M]	68 uH [SRR0906-680ML]	68 uH [SRR4011-680YL]	68 uH [SRU1048-680Y]
68 uH [SRN4026-680M]	68 uH [SRR0908-680ML]	68 uH [SRR4018-680Y]	68 uH [SRU1048A-680Y]
68 uH [SRN6028-680M]	68 uH [SRR1003-680M]	68 uH [SRR4028-680Y]	68 uH [SRU1063-680Y]
68 uH [SRN6045-680M]	68 uH [SRR1005-680Y]	68 uH [SRR5018-680Y]	68 uH [SRU2016-680Y]
68 uH [SRN8040-680M]	68 uH [SRR1205-680YL]	68 uH [SRR5028-680Y]	68 uH [SRU3028-680Y]
68 uH [SRP1770TA-680M]	68 uH [SRR1206-680YL]	68 uH [SRR6028-680Y]	68 uH [SRU5011-680Y]
68 uH [SRP7050TA-680M]	68 uH [SRR1208-680YL]	68 uH [SRR6038-680Y]	68 uH [SRU5016-680Y]
68 uH [SRR0603-680KL]	68 uH [SRR1210-680M]	68 uH [SRR6040A-680M]	68 uH [SRU5018-680Y]
68 uH [SRR0604-680KL]	68 uH [SRR1210A-680M]	68 uH [SRR6603-680ML]	68 uH [SRU5028-680Y]
68 uH [SRR0618-680ML]	68 uH [SRR1240-680M]	68 uH [SRR7032-680M]	68 uH [SRU5028A-680Y]

Multisim 14.1 Education Components

68 uH [SRU6011-680Y]	68.1 kOhm [CRT0603-BY-6812ELF]	680 kOhm [4114R-1-684LF]	680 kOhm [4608X-101-684LF]
68 uH [SRU6018-680Y]	68.1 kOhm [CRT0805-BY-6812ELF]	680 kOhm [4116R-1-684]	680 kOhm [4608X-102-684LF]
68 uH [SRU6025-680Y]	68.1 kOhm [CRT0805-CX-6812ELF]	680 kOhm [4116R-1-684LF]	680 kOhm [4609X-101-684LF]
68 uH [SRU6025A-680Y]	68.1 kOhm [CRT0805-CX-6812ELF]	680 kOhm [4116R-2-684]	680 kOhm [4610X-101-684LF]
68 uH [SRU8028-680Y]	68.1 kOhm [CRT1206-FZ-6812ELF]	680 kOhm [4306R-102-684]	680 kOhm [4610X-102-684LF]
68 uH [SRU8028A-680Y]	68.1 Ohm [CR0402-FX-68R1GLF]	680 kOhm [4306R-102-684LF]	680 kOhm [4814P-T01-684]
68 uH [SRU8043-680Y]	68.1 Ohm [CR0603-FX-68R1ELF]	680 kOhm [4308R-101-684]	680 kOhm [4816P-2-684]
68.1 kOhm [CAY16-6812F4LF]	68.1 Ohm [CR0805-FX-68R1ELF]	680 kOhm [4308R-102-684]	680 kOhm [4816P-T01-684]
68.1 kOhm [CR0201-FW-6812GLF]	68.1 Ohm [CR0805-FX-68R1GLF]	680 kOhm [4308R-102-684LF]	680 kOhm [4816P-T01-684LF]
68.1 kOhm [CR0402-FX-6812GLF]	68.1 Ohm [CR1206-FX-68R1ELF]	680 kOhm [4310R-101-684]	680 kOhm [4816P-T02-684]
68.1 kOhm [CR0603-FX-6812ELF]	68.1 Ohm [CR2512-FX-68R1ELF]	680 kOhm [4310R-101-684LF]	680 kOhm [4816P-T02-684LF]
68.1 kOhm [CR0805-FX-6812ELF]	68.1 Ohm [CRM1206-FX-68R1ELF]	680 kOhm [4310R-102-684]	680 kOhm [4820P-2-684]
68.1 kOhm [CR1206-FX-6812ELF]	68.1 Ohm [CRT0805-BY-68R1ELF]	680 kOhm [4605X-101-684LF]	680 kOhm [4820P-T02-684]
	680 kOhm [4114R-1-684]	680 kOhm [4606X-101-684LF]	680 kOhm [4820P-T02-684LF]
		680 kOhm [4606X-102-684LF]	680 kOhm [CAT16-684J4LF]

Multisim 14.1 Education Components

680 kOhm [CAT16-684J8LF]	680 kOhm [CR1206-JW-684ELF]	680 mOhm [CRL2512-FW-R680ELF]	680 mOhm [PWR4525WR680JE]
680 kOhm [CAT25-684JALF]	680 kOhm [CR1206-JW-684GLF]	680 mOhm [CRL2512-JW-R680ELF]	680 mOhm [PWR6327WR680J]
680 kOhm [CAY10-684J4LF]	680 kOhm [CRM1206-FX-6803ELF]	680 mOhm [CRM1206-FX-R680ELF]	680 mOhm [PWR6327WR680JE]
680 kOhm [CAY16-6803F4LF]	680 mOhm [CRL0603-FW-R680ELF]	680 mOhm [CRM2512-FX-R680ELF]	680 nF [05086C684KAT2A]
680 kOhm [CAY16-684J4LF]	680 mOhm [CRL0603-JW-R680ELF]	680 mOhm [CRM2512-JX-R680ELF]	680 nF [0508ZC684KAT2A]
680 kOhm [CAY16-684J8LF]	680 mOhm [CRL0805-FW-R680ELF]	680 mOhm [PWR1913WR680J]	680 nF [0612YC684KAT2W]
680 kOhm [CR0402-FX-6803GLF]	680 mOhm [CRL0805-JW-R680ELF]	680 mOhm [PWR1913WR680JE]	680 nF [0612ZC684KAT2V]
680 kOhm [CR0402-JW-684GLF]	680 mOhm [CRL1206-FW-R680ELF]	680 mOhm [PWR2615WR680J]	680 nF [C0603C684K4PACT U]
680 kOhm [CR0603-FX-6803ELF]	680 mOhm [CRL1206-JW-R680ELF]	680 mOhm [PWR2615WR680JE]	680 nF [C0603C684K8PACT U]
680 kOhm [CR0603-JW-684ELF]	680 mOhm [CRL2010-FW-R680ELF]	680 mOhm [PWR263S-20-R680F]	680 nF [C0805C684K3PACT U]
680 kOhm [CR0805-FX-6803ELF]	680 mOhm [CRL2010-JW-R680ELF]	680 mOhm [PWR3014WR680F E]	680 nF [C0805C684K4RACT U]
680 kOhm [CR0805-JW-684ELF]	680 mOhm [CRL2010-JW-R680ELF]	680 mOhm [PWR4525WR680J]	680 nF [C0805C684K8RACT U]
680 kOhm [CR1206-FX-6803ELF]			

Multisim 14.1 Education Components

680 nF [C0805C684M4VAC TU]	680 nF [C1210C684M3VAC TU]	680 nF [C1825C684K5RACT U]	680 nF [MDC10684K250A5 5P5TUBE]
680 nF [C1206C684K3RACT U]	680 nF [C1210C684M5VAC TU]	680 nF [C1825C684KARACT U]	680 nF [MDC10684K50A52 P3TUBE]
680 nF [C1206C684K4RACT U]	680 nF [C1210F684K3RACT U]	680 nF [C2220C684K1RACT U]	680 nF [MDC15684K100B5 3P3TUBE]
680 nF [C1206C684K5RACT U]	680 nF [C1210F684K4RACT U]	680 nF [C2220C684K5RACT U]	680 nF [MDC15684K250B5 3P3TUBE]
680 nF [C1206C684K8RACT U]	680 nF [C1210F684K5RACT U]	680 nF [C2220C684KARACT U]	680 nF [MDC15684K50B53 P3TUBE]
680 nF [C1206C684M3VAC TU]	680 nF [C1812C684K5RACT U]	680 nF [C2225C684K1RACT U]	680 nF [MDK10684K50A52 P3TUBE]
680 nF [C1206C684M4VAC TU]	680 nF [C1812C684M5UAC TU]	680 nF [C2225C684K5RACT U]	680 nF [MDK15684K250B5 3P3TUBE]
680 nF [C1206F684K4RACT U]	680 nF [C1812F684K1RACT U]	680 nF [C2225C684KARACT U]	680 nF [MDS10684K100A5 2P3TUBE]
680 nF [C1210C684K3RACT U]	680 nF [C1812F684K3RACT U]	680 nF [MDC10684K100A5 2P3TUBE]	680 nF [MDS10684K50A52 P3TUBE]
680 nF [C1210C684K4RACT U]	680 nF [C1812F684K5RACT U]	680 nF [MDC10684K250A5 5P3TUBE]	680 nF [MDS15684K100B5 3P3TUBE]
680 nF [C1210C684K5RACT U]	680 nF [C1825C684K1RACT U]	680 nF [MDC10684K250A5 5P4TUBE]	680 nF [MDS15684K250B5 3P3TUBE]

Multisim 14.1 Education Components

680 nF [MDS15684K50B53 P3TUBE]	680 nF [T496C684M050AT 6110]	680 nF [THJB684K035RJN]	680 nH [SRP1250- R68M]
680 nF [SPC16.5684K100C 31TR24]	680 nF [TAJA684K025RNJ]	680 nF [TPSA684K025R600 0]	680 nH [SRP1265A- R68M]
680 nF [T491A684M020AT]	680 nF [TAJA684K035RNJ]	680 nF [TPSA684K035R600 0]	680 nH [SRP1270- R68M]
680 nF [T491A684M025AT]	680 nF [TAJB684K035RNJ]	680 nF [TPSB684K050R400 0]	680 nH [SRP4020- R68M]
680 nF [T491A684M035AT]	680 nF [TAJC684K050RNJ]	680 nF [TRJA684K025RRJ]	680 nH [SRP4020TA-R68M]
680 nF [T491B684M035AT]	680 nF [TAJR684K016RNJ]	680 nF [W2L1ZC684MAT1A]	680 nH [SRP5015TA-R68M]
680 nF [T491B684M050AT]	680 nF [TAJR684K020RNJ]	680 nF [W3L16C684MAT1S]	680 nH [SRP5030TA-R68M]
680 nF [T491C684M050AT]	680 nF [TAJS684K016RNJ]	680 nF [W3L16C684MAT1S]	680 nH [SRP5030T- R68M]
680 nF [T494A684M020AT]	680 nF [TAJS684K020RNJ]	680 nH [SDR1005- R68ML]	680 nH [SRP6540- R68M]
680 nF [T494A684M025AT]	680 nF [TAJS684K025RNJ]	680 nH [SRN2010- R68M]	680 nH [SRP7028A- R68M]
680 nF [T494A684M035AT]	680 nF [TAJS684K035RNJ]	680 nH [SRN2510- R68M]	680 nH [SRP7030- R68FM]
680 nF [T494B684M035AT]	680 nF [TAJT684K020RNJ]	680 nH [SRN2512- R68M]	680 nH [SRP7050TA-R68M]
680 nF [T494B684M050AT]	680 nF [TAJT684K035RNJ]	680 nH [SRP1040- R68M]	680 Ohm [4114R-1- 681]
680 nF [T494C684M050AT]	680 nF [THJA684K025RJN]	680 nH [SRP1235- R68M]	680 Ohm [4114R-1- 681LF]
			680 Ohm [4114R-2- 681]

Multisim 14.1 Education Components

680 Ohm [4114R-2-681LF]	680 Ohm [4308M-101-681]	680 Ohm [4310R-102-681]	680 Ohm [4606X-102-681LF]
680 Ohm [4116R-1-681]	680 Ohm [4308M-101-681LF]	680 Ohm [4310R-102-681LF]	680 Ohm [4607X-101-681LF]
680 Ohm [4116R-1-681LF]	680 Ohm [4308R-101-681]	680 Ohm [4416P-1-681]	680 Ohm [4608H-102-681LF]
680 Ohm [4116R-2-681]	680 Ohm [4308R-101-681LF]	680 Ohm [4416P-2-681]	680 Ohm [4608X-101-681LF]
680 Ohm [4116R-2-681LF]	680 Ohm [4308R-102-681]	680 Ohm [4416P-2-681LF]	680 Ohm [4608X-102-681LF]
680 Ohm [4304M-102-681]	680 Ohm [4308R-102-681LF]	680 Ohm [4416P-T01-681]	680 Ohm [4608X-AP2-681LF]
680 Ohm [4304M-102-681LF]	680 Ohm [4309R-101-681]	680 Ohm [4416P-T02-681]	680 Ohm [4609M-101-681LF]
680 Ohm [4306H-102-681]	680 Ohm [4309R-101-681LF]	680 Ohm [4420P-2-681]	680 Ohm [4609X-101-681LF]
680 Ohm [4306H-102-681LF]	680 Ohm [4310H-101-681]	680 Ohm [4420P-T01-681]	680 Ohm [4609X-AP1-681LF]
680 Ohm [4306R-101-681]	680 Ohm [4310H-101-681LF]	680 Ohm [4420P-T02-681]	680 Ohm [4610H-101-681LF]
680 Ohm [4306R-101-681LF]	680 Ohm [4310M-101-681]	680 Ohm [4604X-101-681LF]	680 Ohm [4610X-101-681LF]
680 Ohm [4306R-102-681]	680 Ohm [4310M-101-681LF]	680 Ohm [4604X-102-681LF]	680 Ohm [4610X-102-681LF]
680 Ohm [4306R-102-681LF]	680 Ohm [4310M-102-681]	680 Ohm [4605X-101-681LF]	680 Ohm [4610X-AP1-681LF]
680 Ohm [4308H-101-681]	680 Ohm [4310R-101-681]	680 Ohm [4606H-102-681LF]	680 Ohm [4611X-101-681LF]
680 Ohm [4308H-101-681LF]	680 Ohm [4310R-101-681LF]	680 Ohm [4606X-101-681LF]	680 Ohm [4612X-102-681LF]

Multisim 14.1 Education Components

680 Ohm [4814P-2-681]	680 Ohm [CAT10-681J4LF]	680 Ohm [CR0603-JW-681ELF]	680 Ohm [PWR163S-25-6800JE]
680 Ohm [4814P-2-681LF]	680 Ohm [CAT16-6800F4LF]	680 Ohm [CR0805-FX-6800ELF]	680 Ohm [PWR2615W6800J]
680 Ohm [4814P-T01-681]	680 Ohm [CAT16-681J2LF]	680 Ohm [CR0805-FX-6800GLF]	680 Ohm [PWR2615W6800JE]
680 Ohm [4814P-T01-681LF]	680 Ohm [CAT16-681J4LF]	680 Ohm [CR0805-JW-681ELF]	680 Ohm [PWR4525W6800J]
680 Ohm [4814P-T02-681]	680 Ohm [CAT16-681J8LF]	680 Ohm [CR1206-FX-6800ELF]	680 Ohm [PWR4525W6800JE]
680 Ohm [4816P-1-681]	680 Ohm [CAT25-681JALF]	680 Ohm [CR1206-FX-6800GLF]	680 Ohm [PWR6327W6800J]
680 Ohm [4816P-1-681LF]	680 Ohm [CAY10-681J4LF]	680 Ohm [CR1206-JW-681ELF]	680 Ohm [PWR6327W6800JE]
680 Ohm [4816P-2-681]	680 Ohm [CAY16-6800F4LF]	680 Ohm [CR1206-JW-681GLF]	680 pF [C0402C681K1HACTU]
680 Ohm [4816P-2-681LF]	680 Ohm [CAY16-681J4LF]	680 Ohm [CR2010-JW-681ELF]	680 pF [C0402C681K3GACTU]
680 Ohm [4816P-T01-681]	680 Ohm [CAY16-681J8LF]	680 Ohm [CR2512-JW-681ELF]	680 pF [C0402C681K3HACTU]
680 Ohm [4816P-T01-681LF]	680 Ohm [CAY17-681JALF]	680 Ohm [CRM1206-FX-6800ELF]	680 pF [C0402C681K3RACTU]
680 Ohm [4816P-T02-681]	680 Ohm [CR0201-FW-6800GLF]	680 Ohm [CRM2512-JW-681ELF]	680 pF [C0402C681K4RACTU]
680 Ohm [4816P-T02-681LF]	680 Ohm [CR0402-FX-6800GLF]	680 Ohm [CRT0805-DY-6800ELF]	
680 Ohm [4820P-1-681]	680 Ohm [CR0402-JW-681GLF]	680 Ohm [PWR163S-25-6800F]	
680 Ohm [4820P-T01-681]	680 Ohm [CR0603-FX-6800ELF]		

Multisim 14.1 Education Components

680 pF [C0402C681K5HACT U]	680 pF [C0603C681K5RACT U]	680 pF [C1206C681KCGAC TU]	680 pF [GPC7.3682K630K3 7TR12]
680 pF [C0402C681K5RACT U]	680 pF [C0805C681K1GACT U]	680 pF [C1210C681KBGAC TU]	680 pF [SPC7.3681K100K31 TR12]
680 pF [C0603C681K1HACT U]	680 pF [C0805C681K1RACT U]	680 pF [C1210C681KCGAC TU]	680 pF [SPC7.3681K250K31 TR12]
680 pF [C0603C681K1RACT U]	680 pF [C0805C681K2RACT U]	680 pF [C1210C681KDGAC TU]	680 pF [SPC7.3681K400K31 TR12]
680 pF [C0603C681K2RACT U]	680 pF [C0805C681K4GACT U]	680 pF [C1812C681KBGAC TU]	680 pF [SPC7.3681K630K31 TR12]
680 pF [C0603C681K3GACT U]	680 pF [C0805C681K4RACT U]	680 pF [C1825C681KBGAC TU]	680 uF [2R5TPE680MCL]
680 pF [C0603C681K3HACT U]	680 pF [C0805C681K5GACT U]	680 pF [C2220C681KBGAC TU]	680 uF [2R5TPE680MFL]
680 pF [C0603C681K3RACT U]	680 pF [C0805C681K5RACT U]	680 pF [C2220C681KZGACT U]	680 uF [2R5TPF680M6L]
680 pF [C0603C681K4RACT U]	680 pF [C1206C681K1GACT U]	680 pF [C2225C681KBGAC TU]	680 uF [2R5TPF680ML]
680 pF [C0603C681K5GACT U]	680 pF [C1206C681K2GACT U]	680 pF [GPC7.3681K160K3 1TR12]	680 uF [4TPF680MAH]
680 pF [C0603C681K5HACT U]	680 pF [C1206C681K5GACT U]	680 pF [GPC7.3681K63K31 TR12]	680 uF [6TPE680M]
			680 uF [6TPE680MI]
			680 uF [ETPF680M5H]

Multisim 14.1 Education Components

680 uF [T491D687M004AT]	680 uF [T513X687M004AH 6110]	680 uF [T520X687M004AT E010]	680 uF [T530D687M2R5AT E006]
680 uF [T491E687M006AT]	680 uF [T513X687M006AH 6110]	680 uF [T520X687M004AT E015]	680 uF [T530D687M2R5AT E010]
680 uF [T491X687M004AT]	680 uF [T513X687M006AH 6120]	680 uF [T520X687M004AT E035]	680 uF [T530X687M004AT E004]
680 uF [T494D687M004AT]	680 uF [T520D687M003AT E015]	680 uF [T520Y687M004AT E010]	680 uF [T530X687M004AT E006]
680 uF [T494E687M006AT]	680 uF [T520D687M003AT E040]	680 uF [T520Y687M004AT E015]	680 uF [T530X687M004AT E010]
680 uF [T510E687M006AT E012]	680 uF [T520D687M004AT E012]	680 uF [T520Y687M004AT E025]	680 uF [T530X687M006AT E010]
680 uF [T510E687M006AT E023]	680 uF [T520D687M004AT E015]	680 uF [T520Y687M2R5AT E015]	680 uF [T530X687M006AT E018]
680 uF [T510X687M004AT E030]	680 uF [T520D687M004AT E025]	680 uF [T520Y687M2R5AT E025]	680 uF [T530Y687M004AT E005]
680 uF [T510X687M006AT E023]	680 uF [T520D687M2R5AT E010]	680 uF [T525D687M003AT E025]	680 uF [T530Y687M2R5AT E006]
680 uF [T513E687M006AH 6110]	680 uF [T520D687M2R5AT E015]	680 uF [T525D687M2R5AT E025]	680 uF [T543X687M004AT E015]
680 uF [T513E687M006AH 6120]	680 uF [T520D687M2R5AT E040]	680 uF [T530D687M003AT E010]	680 uF [TAJC687K002RNJ] 680 uF [TAJD687K004RNJ]

Multisim 14.1 Education Components

680 uF [TAJE687K004RNJ]	680 uF [TPSE687K006R004 5]	680 uH [SDR0805- 681KL]	680 uH [SRR0735A- 681M]
680 uF [TAJE687K006RNJ]	680 uF [TPSE687K006R006 0]	680 uH [SDR0906- 681KL]	680 uH [SRR0745A- 681M]
680 uF [TAJV687K006RNJ]	680 uF [TPSE687K006R010 0]	680 uH [SDR1005- 681KL]	680 uH [SRR0805- 681K]
680 uF [TPME687K004R00 18]	680 uF [TPSV687K006R003 5]	680 uH [SDR1006- 681KL]	680 uH [SRR0906- 681YL]
680 uF [TPME687K004R00 23]	680 uF [TPSV687K006R004 0]	680 uH [SDR1030- 681K]	680 uH [SRR0908- 681YL]
680 uF [TPME687K006R00 18]	680 uF [TPSV687K006R005 0]	680 uH [SDR1045- 681K]	680 uH [SRR1005- 681K]
680 uF [TPME687K006R00 23]	680 uF [TRME687K004R00 23]	680 uH [SDR1305- 681K]	680 uH [SRR1205- 681KL]
680 uF [TPMV687K006R00 23]	680 uH [SDE1006A- 681K]	680 uH [SDR1307- 681KL]	680 uH [SRR1206- 681KL]
680 uF [TPSD687K004R010 0]	680 uH [SDR0302- 681KL]	680 uH [SDR1307A-681K]	680 uH [SRR1208- 681KL]
680 uF [TPSE687K004R004 0]	680 uH [SDR0403- 681KL]	680 uH [SDR1806- 681KL]	680 uH [SRR1210- 681M]
680 uF [TPSE687K004R006 0]	680 uH [SDR0503- 681KL]	680 uH [SDR6603- 681M]	680 uH [SRR1210A- 681M]
680 uF [TPSE687K004R010 0]	680 uH [SDR0604- 681KL]	680 uH [SDR7030- 681K]	680 uH [SRR1240- 681K]
	680 uH [SDR0703- 681KL]	680 uH [SDR7045- 681K]	680 uH [SRR1260- 681K]
		680 uH [SRR0603- 681KL]	680 uH [SRR1260A- 681K]
		680 uH [SRR0604- 681KL]	680 uH [SRR1280- 681K]

Multisim 14.1 Education Components

680 uH [SRR1806-681M]	681 Ohm [CR0603-FX-6810ELF]	69.8 kOhm [CRT0603-BY-6982ELF]	698 Ohm [CR0603-FX-6980ELF]
680 uH [SRR5028-681Y]	681 Ohm [CR0805-FX-6810ELF]	69.8 kOhm [CRT0805-FY-6982ELF]	698 Ohm [CR0805-FX-6980ELF]
680 uH [SRR6028-681Y]	681 Ohm [CR1206-FX-6810ELF]	69.8 Ohm [CR0201-FW-69R8GLF]	698 Ohm [CR1206-FX-6980ELF]
680 uH [SRR6603-681ML]	681 Ohm [CRM1206-FX-6810ELF]	69.8 Ohm [CR0402-FX-69R8GLF]	6DJ8
680 uH [SRR7032-681M]	681 Ohm [CRT0402-FZ-6810GLF]	69.8 Ohm [CR0603-FX-69R8ELF]	6F6
680 uH [SRR7045-681M]	681 Ohm [CRT0805-FV-6810ELF]	69.8 Ohm [CR0805-FX-69R8ELF]	6HP04CH-TL-W
681 kOhm [CAY16-6813F4LF]	6.85119E+11	69.8 Ohm [CR1206-FX-69R8ELF]	6J5
681 kOhm [CR0402-FX-6813GLF]	69.8 kOhm [CR0402-FX-6982GLF]	690-009-521-900	6L6GC
681 kOhm [CR0603-FX-6813ELF]	69.8 kOhm [CR0603-FX-6982ELF]	698 kOhm [CR0402-FX-6983GLF]	6Line_Bussed
681 kOhm [CR0805-FX-6813ELF]	69.8 kOhm [CR0805-FX-6982ELF]	698 kOhm [CR0603-FX-6983ELF]	6Line_Isolated
681 kOhm [CR1206-FX-6813ELF]	69.8 kOhm [CR1206-FX-6982ELF]	698 kOhm [CR0805-FX-6983ELF]	6N1136
681 kOhm [CRT1206-FZ-6813ELF]	69.8 kOhm [CRM2512-FX-6982ELF]	698 Ohm [CR0402-FX-6980GLF]	6N1136-X006
681 Ohm [CR0402-FX-6810GLF]			6N1136-X009T
			6N136
			6N136-000E
			6N136-020E
			6N136-060E
			6N136-300E
			6N136-320E
			6N136-360E
			6N136-X001
			6N136-X006
			6N136-X007T

Multisim 14.1 Education Components

6N136-X009T	7 mOhm [CRE2512-FZ-R007E-3]	7.32 kOhm [CR1206-FX-7321ELF]	7.5 kOhm [4610X-101-752LF]
6N136-X016			
6N136-X017T	7 mOhm [CRF2512-FX-R007ELF]	7.32 kOhm [CRT0603-BY-7321ELF]	7.5 kOhm [CAY16-7501F4LF]
6N136-X019T	7 mOhm [CRF2512-JX-R007ELF]		7.5 kOhm [CAY16-752J4LF]
6N137		7.4 uH [SRP1205-7R2Y]	7.5 kOhm [CR0201-JW-752GLF]
6N137-X006	7 Ohm [PWR6327W7R00F]		
6N137-X007T	7 uH [SRR1005-7R0M]	7.4 uH [SRR6038-7R4Y]	7.5 kOhm [CR0402-FX-7501GLF]
6N139-000E		7.5 kOhm [4114R-1-752]	7.5 kOhm [CR0402-JW-752GLF]
6N139-020E	7.15 kOhm [CR0402-FX-7151GLF]	7.5 kOhm [4116R-1-752]	7.5 kOhm [CR0603-FX-7501ELF]
6N139-060E			
6N139-300E	7.15 kOhm [CR0603-FX-7151ELF]	7.5 kOhm [4116R-1-752LF]	7.5 kOhm [CR0603-JW-752ELF]
6N139-320E			
6N139-360E	7.15 kOhm [CR0805-FX-7151ELF]	7.5 kOhm [4308R-101-752]	7.5 kOhm [CR0805-FX-7501ELF]
6POS_ROTARY		7.5 kOhm [4308R-102-752]	7.5 kOhm [CR0805-FX-7501GLF]
6SF5	7.15 kOhm [CR1206-FX-7151ELF]	7.5 kOhm [4308R-102-752LF]	7.5 kOhm [CR0805-JW-752ELF]
6SL7GT			
6SN7GTB	7.3 uH [SRR6028-7R3Y]	7.5 kOhm [4310M-102-752]	7.5 kOhm [CR1206-FX-7501ELF]
6STEP_DECODER			
6TQ045	7.32 kOhm [CR0402-FX-7321GLF]	7.5 kOhm [4310M-102-752LF]	7.5 kOhm [CR1206-JW-752ELF]
6V6GTA			
7 kOhm [4116R-2-702]	7.32 kOhm [CR0603-FX-7321ELF]	7.5 kOhm [4310R-101-752]	7.5 kOhm [CR2010-FX-7501ELF]
7 kOhm [4816P-2-702]		7.5 kOhm [4606X-102-752LF]	7.5 kOhm [CRM0805-FX-7501ELF]
7 mOhm [CRE2512-FZ-R007E-2]	7.32 kOhm [CR0805-FX-7321ELF]	7.5 kOhm [4608X-102-752LF]	

Multisim 14.1 Education Components

7.5 kOhm [CRT0402-FZ- 7501GLF]	7.5 MOhm [CR0805-JW- 755ELF]	7.5 nF [CDR34BP752AKSM]	7.5 Ohm [CRL1206- JW-7R50ELF]
7.5 kOhm [CRT0603-BY- 7501ELF]	7.5 MOhm [CR1206-JW- 755ELF]	7.5 Ohm [CAT10- 7R5J4LF]	7.5 Ohm [CRL2010- FW-7R50ELF]
7.5 kOhm [CRT0603-DY- 7501ELF]	7.5 nF [C0603C752K3HACT U]	7.5 Ohm [CAT16- 7R5J4GLF]	7.5 Ohm [CRL2010- JW-7R50ELF]
7.5 kOhm [CRT0805-BY- 7501ELF]	7.5 nF [C0805C752K1GACT U]	7.5 Ohm [CAT16- 7R5J4LF]	7.5 Ohm [CRL2512- FW-7R50ELF]
7.5 kOhm [CRT0805-DZ- 7501ELF]	7.5 nF [C0805C752K1HACT U]	7.5 Ohm [CAY10- 7R5J2LF]	7.5 Ohm [CRM1206-FX- 7R50ELF]
7.5 kOhm [CRT0805-PV- 7501ELF]	7.5 nF [C0805C752K3HACT U]	7.5 Ohm [CR0402- J/-7R5GLF]	7.5 Ohm [CRM2010-JW- 7R5ELF]
7.5 kOhm [PWR163S-25- 7501JE]	7.5 nF [C0805C752K5GACT U]	7.5 Ohm [CR0603- J/-7R5ELF]	7.5 Ohm [CRM2512-JW- 7R5ELF]
7.5 kOhm [PWR221T-30- 7501F]	7.5 nF [C0805C752K5HACT U]	7.5 Ohm [CR0805- J/-7R5ELF]	7.5 Ohm [CRT0603- BY-7R50ELF]
7.5 kOhm [PWR221T-30- 7501J]	7.5 nF [C1206C752K1HACT U]	7.5 Ohm [CR1206- J/-7R5ELF]	7.5 Ohm [FW10A7R50JA]
7.5 kOhm [PWR263S-35- 7501JE]	7.5 nF [C1206C752K3HACT U]	7.5 Ohm [CRL0603- FW-7R50ELF]	7.5 Ohm [FW20A7R50JA]
7.5 MOhm [CR0603-JW- 755ELF]	7.5 nF [C1206C752K5HACT U]	7.5 Ohm [CRL0603- JW-7R50ELF]	7.5 Ohm [FW70A7R50JA]
		7.5 Ohm [CRL0805- FW-7R50ELF]	7.5 Ohm [PWR163S-25- 7R50F]
		7.5 Ohm [CRL0805- JW-7R50ELF]	7.5 Ohm [PWR163S-25- 7R50FE]
		7.5 Ohm [CRL1206- FW-7R50ELF]	

Multisim 14.1 Education Components

7.5 Ohm [PWR163S-25-7R50J]	7.5 Ohm [PWR263S-20-7R50J]	7.5 uH [SDR0805-7R5ML]	7.68 kOhm [CR1206-FX-7681ELF]
7.5 Ohm [PWR1913W7R50J]	7.5 Ohm [PWR263S-20-7R50JE]	7.5 uH [SRR0804-7R5M]	7.8 uH [SRP1250-7R8M]
7.5 Ohm [PWR1913W7R50JE]	7.5 Ohm [PWR263S-35-7R50F]	7.5 uH [SRR0908-7R5ML]	7.87 kOhm [CR0402-FX-7871GLF]
7.5 Ohm [PWR2010W7R50JE]	7.5 Ohm [PWR263S-35-7R50J]	7.5 uH [SRR1205-7R5ML]	7.87 kOhm [CR0603-FX-7871ELF]
7.5 Ohm [PWR220T-20-7R50F]	7.5 Ohm [PWR3014W7R50JE]	7.5 uH [SRR1206-7R5ML]	7.87 kOhm [CR0805-FX-7871ELF]
7.5 Ohm [PWR220T-20-7R50J]	7.5 Ohm [PWR4318W7R50JE]	7.5 uH [SRR1280-7R5Y]	7.87 kOhm [CR0805-FX-7871GLF]
7.5 Ohm [PWR220T-35-7R50J]	7.5 Ohm [PWR4525W7R50J]	7.6 uH [SRR1260-7R6Y]	7.87 kOhm [CR1206-FX-7871ELF]
7.5 Ohm [PWR221T-30-7R50F]	7.5 Ohm [PWR4525W7R50JE]	7.6 uH [SRR1260A-7R6Y]	7.87 kOhm [CRM0805-FX-7871ELF]
7.5 Ohm [PWR221T-30-7R50J]	7.5 Ohm [PWR5322W7R50JE]	7.6 uH [SRR1280-7R6Y]	7.87 kOhm [CRT0402-FZ-7871GLF]
7.5 Ohm [PWR2615W7R50JE]	7.5 Ohm [PWR6327W7R50J]	7.68 kOhm [CR0402-FX-7681GLF]	7.87 kOhm [CRT0603-BX-7871ELF]
7.5 Ohm [PWR263S-20-7R50F]	7.5 Ohm [PWR6327W7R50JE]	7.68 kOhm [CR0603-FX-7681ELF]	7.87 kOhm [CRT0603-BY-7871ELF]
	7.5 uH [SDR0603-7R5ML]	7.68 kOhm [CR0805-FX-7681ELF]	

Multisim 14.1 Education Components

7.87 Ohm [CRM2512-FX- 7R87ELF]	71.5 Ohm [CR0603- FX-71R5ELF]	715 Ohm [CRT0805-BY- 7150ELF]	732 kOhm [CR1206-FX- 7323ELF]
70 mOhm [CRA2512-FZ- R070ELF]	71.5 Ohm [CR0805- FX-71R5ELF]	73.2 kOhm [CR0402-FX- 7322GLF]	732 Ohm [CR0402- FX-7320GLF]
70 mOhm [CRA2512-JZ- R070ELF]	71.5 Ohm [CR1206- FX-71R5ELF]	73.2 kOhm [CR0603-FX- 7322ELF]	732 Ohm [CR0603- FX-7320ELF]
70 mOhm [CRL2512-FW- R070ELF]	715 kOhm [CR0402-FX- 7153GLF]	73.2 kOhm [CR0805-FX- 7322ELF]	732 Ohm [CR0805- FX-7320ELF]
700 mOhm [CRL0603-FW- R700ELF]	715 kOhm [CR0603-FX- 7153ELF]	73.2 kOhm [CR1206-FX- 7322ELF]	732 Ohm [CR1206- FX-7320ELF]
700 nH [SRP1206- R47Y]	715 kOhm [CR0805-FX- 7153ELF]	73.2 kOhm [CR1206-FX- 7322ELF]	732 Ohm [CRT0603-PV- 7320ELF]
71.5 kOhm [CRO201-FW- 7152GLF]	715 kOhm [CR1206-FX- 7153ELF]	73.2 Ohm [CR0805- FX-73R2ELF]	73391-0060
71.5 kOhm [CR0201-FW- 7152GLF]	715 Ohm [CAY16- 7150F4LF]	73.2 Ohm [CR1206- FX-73R2ELF]	7400N
71.5 kOhm [CR0402-FX- 7152GLF]	715 Ohm [CR0402- FX-7150GLF]	73.2 Ohm [CR2010- FX-73R2ELF]	7401N
71.5 kOhm [CR0603-FX- 7152ELF]	715 Ohm [CR0603- FX-7150ELF]	730 Ohm [4116R-1- 731]	7402N
71.5 kOhm [CR0805-FX- 7152ELF]	715 Ohm [CR0805- FX-7150ELF]	732 kOhm [CR1206-FX- 7323GLF]	7403N
71.5 kOhm [CR1206-FX- 7152ELF]	715 Ohm [CR1206- FX-7150ELF]	732 kOhm [CR0603-FX- 7323ELF]	7404N
71.5 Ohm [CR0402- FX-71R5GLF]	715 Ohm [CRT0603-BW- 7150ELF]	732 kOhm [CR0805-FX- 7323ELF]	7405N
			7406N
			7407N
			7408J
			7408N
			7409N
			741
			74100J

Multisim 14.1 Education Components

74100N	74160N	741-DIV	74320-3004
74107N	74161N	7420N	74320-4004
74109N	74162N	7422N	74320-5000
7410N	74163N	74246N	7432N
74116N	74164N	74247N	7433N
74125N	74165N	74248J	74351N
74126N	74166N	74248N	74365N
7412N	7416N	74249J	74366N
74132N	74173N	74249N	74367N
74136N	74174N	74251J	74368N
7413N	74175N	74251N	7437N
74145N	7417N	74259N	7438N
74147N	74180N	7425N	74390N
74148N	74181J	7426N	74393N
7414N	74181N	74273DW	7439N
74150N	74182J	74273N	7440N
74151N	74182N	74279N	74425N
74152AJ	74190N	7427N	74426N
74152AN	74191N	74283N	7442N
74153N	74192N	7428N	7443J
74154N	74193N	74290N	7443N
74155N	74194N	74293N	7444J
74156N	74195N	74298N	7444N
74157N	74198N	7430N	7445N
74159N	74199N	74320-1004	7446N

Multisim 14.1 Education Components

7447N	74ALS03BN	74ALS151M	74ALS21AN
7448N	74ALS04BM	74ALS151N	74ALS240AN
7451N	74ALS04BN	74ALS153M	74ALS240AWM
7454N	74ALS05AM	74ALS153N	74ALS241AN
7472N	74ALS05AN	74ALS157M	74ALS241AWM
7473N	74ALS08M	74ALS157N	74ALS244AN
7474N	74ALS08N	74ALS158M	74ALS244AWM
7475N	74ALS09M	74ALS158N	74ALS245AN
7476N	74ALS09N	74ALS161BM	74ALS245AWM
7477W	74ALS109AM	74ALS161BN	74ALS251M
7482J	74ALS109AN	74ALS162BM	74ALS251N
7482N	74ALS10AM	74ALS162BN	74ALS253M
7483N	74ALS10AN	74ALS163BM	74ALS253N
7485N	74ALS11AM	74ALS163BN	74ALS257M
7486N	74ALS11AN	74ALS165M	74ALS257N
749070-9	74ALS125M	74ALS165N	74ALS258M
7490N	74ALS125N	74ALS169M	74ALS258N
7491N	74ALS133M	74ALS169N	74ALS273N
7492N	74ALS133N	74ALS174M	74ALS273WM
7493N	74ALS137M	74ALS174N	74ALS27M
74ALS00M	74ALS137N	74ALS175M	74ALS27N
74ALS00N	74ALS138M	74ALS175N	74ALS30AM
74ALS02M	74ALS138N	74ALS20AM	74ALS30AN
74ALS02N	74ALS14M	74ALS20AN	74ALS32M
74ALS03BM	74ALS14N	74ALS21AM	74ALS32N

Multisim 14.1 Education Components

74ALS373N	74AS161N	74AS30N	74F112N
74ALS373WM	74AS163M	74AS32M	74F113D
74ALS374AN	74AS163N	74AS32N	74F113N
74ALS374AWM	74AS169AM	74AS34N	74F114D
74ALS37AM	74AS169AN	74AS373N	74F114N
74ALS37AN	74AS174N	74AS373WM	74F11D
74ALS38AM	74AS181BN	74AS374N	74F11N
74ALS38AN	74AS181BNT	74AS374WM	74F125D
74ALS74AM	74AS21M	74AS74M	74F125N
74ALS74AN	74AS21N	74AS74N	74F126D
74ALS86M	74AS240N	74AS86M	74F126N
74ALS86N	74AS240WM	74AS86N	74F138D
74AS00M	74AS244N	74F00D	74F138N
74AS00N	74AS244WM	74F00N	74F139D
74AS04M	74AS245N	74F02D	74F139N
74AS04N	74AS245WM	74F02N	74F13D
74AS08M	74AS257M	74F04D	74F13N
74AS08N	74AS257N	74F04N	74F148D
74AS10M	74AS258M	74F08D	74F148N
74AS10N	74AS258N	74F08N	74F14D
74AS157M	74AS27M	74F109D	74F14N
74AS157N	74AS27N	74F109N	74F151D
74AS158M	74AS280M	74F10D	74F151N
74AS158N	74AS280N	74F10N	74F153D
74AS161M	74AS30M	74F112D	74F153N

Multisim 14.1 Education Components

74F157AD	74F182D	74F243N	74F32D
74F157AN	74F182N	74F244D	74F32N
74F157D	74F190D	74F244N	74F350D
74F157N	74F190N	74F245D	74F350N
74F158AD	74F191D	74F245N	74F352D
74F158AN	74F191N	74F251D	74F352N
74F158D	74F192D	74F251N	74F353D
74F158N	74F192N	74F253D	74F353N
74F160AD	74F193D	74F253N	74F365D
74F160AN	74F193N	74F257D	74F365N
74F161AD	74F194D	74F257N	74F366D
74F161AN	74F194N	74F258AD	74F366N
74F162AD	74F195D	74F258AN	74F367D
74F162AN	74F195N	74F258D	74F367N
74F163AD	74F20D	74F258N	74F368D
74F163AN	74F20N	74F259D	74F368N
74F164D	74F21D	74F259N	74F373D
74F164N	74F21N	74F273PC	74F373N
74F169D	74F240D	74F273SC	74F374D
74F169N	74F240N	74F27M	74F374N
74F174D	74F241D	74F27N	74F378D
74F174N	74F241N	74F280D	74F378N
74F175D	74F242D	74F280N	74F379D
74F175N	74F242N	74F283D	74F379N
74F181N	74F243D	74F283N	74F37D

Multisim 14.1 Education Components

74F37N	74F574PC	74HC00N_2V	74HC04N_4V
74F38D	74F574SC	74HC00N_4V	74HC04N_6V
74F38N	74F640PC	74HC00N_6V	74HC05D_2V
74F399D	74F640SC	74HC01D_2V	74HC05D_4V
74F399N	74F645PC	74HC01D_4V	74HC05D_6V
74F40D	74F645SC	74HC01D_6V	74HC05N_2V
74F40N	74F74D	74HC01N_2V	74HC05N_4V
74F51D	74F74N	74HC01N_4V	74HC05N_6V
74F51N	74F821PC	74HC01N_6V	74HC08D_2V
74F521DW	74F821SPC	74HC02D_2V	74HC08D_4V
74F521N	74F823PC	74HC02D_4V	74HC08D_6V
74F533PC	74F823SPC	74HC02D_6V	74HC08N_2V
74F533SC	74F825PC	74HC02N_2V	74HC08N_4V
74F534PC	74F825SPC	74HC02N_4V	74HC08N_6V
74F534SC	74F827PC	74HC02N_6V	74HC09D_2V
74F540PC	74F827SPC	74HC03D_2V	74HC09D_4V
74F540SC	74F828PC	74HC03D_4V	74HC09D_6V
74F541PC	74F828SPC	74HC03D_6V	74HC09N_2V
74F541SC	74F85D	74HC03N_2V	74HC09N_4V
74F563PC	74F85N	74HC03N_4V	74HC09N_6V
74F563SC	74F86D	74HC03N_6V	74HC107D_2V
74F564PC	74F86N	74HC04D_2V	74HC107D_4V
74F564SC	74HC00D_2V	74HC04D_4V	74HC107D_6V
74F573PC	74HC00D_4V	74HC04D_6V	74HC107N_2V
74F573SC	74HC00D_6V	74HC04N_2V	74HC107N_4V

Multisim 14.1 Education Components

74HC107N_6V	74HC114D_2V	74HC137D_2V	74HC148DW_6V
74HC109D_2V	74HC114D_4V	74HC137D_4V	74HC148N_2V
74HC109D_4V	74HC114D_6V	74HC137D_6V	74HC148N_4V
74HC109D_6V	74HC114N_2V	74HC137N_2V	74HC148N_6V
74HC109N_2V	74HC114N_4V	74HC137N_4V	74HC14D_2V
74HC109N_4V	74HC114N_6V	74HC137N_6V	74HC14D_4V
74HC109N_6V	74HC11D_2V	74HC138D_2V	74HC14D_6V
74HC10D_2V	74HC11D_4V	74HC138D_4V	74HC14N_2V
74HC10D_4V	74HC11D_6V	74HC138D_4V	74HC14N_4V
74HC10D_6V	74HC11N_2V	74HC138D_6V	74HC14N_6V
74HC10N_2V	74HC11N_4V	74HC138N_2V	74HC151D_2V
74HC10N_4V	74HC11N_6V	74HC138N_4V	74HC151D_4V
74HC10N_6V	74HC125N_2V	74HC138N_4V	74HC151D_6V
74HC112D_2V	74HC125N_4V	74HC138N_6V	74HC151N_2V
74HC112D_4V	74HC125N_6V	74HC139DW_2V	74HC151N_4V
74HC112D_6V	74HC126N_2V	74HC139DW_4V	74HC151N_6V
74HC112N_2V	74HC126N_4V	74HC139DW_6V	74HC152D_2V
74HC112N_4V	74HC126N_6V	74HC139N_2V	74HC152D_4V
74HC112N_6V	74HC133D_2V	74HC139N_4V	74HC152D_6V
74HC113D_2V	74HC133D_4V	74HC139N_6V	74HC152N_2V
74HC113D_4V	74HC133D_4V	74HC147N_2V	74HC152N_4V
74HC113D_6V	74HC133D_6V	74HC147N_4V	74HC152N_6V
74HC113N_2V	74HC133N_2V	74HC147N_6V	74HC153D_2V
74HC113N_4V	74HC133N_4V	74HC148DW_2V	74HC153D_4V
74HC113N_6V	74HC133N_6V	74HC148DW_4V	74HC153D_6V

Multisim 14.1 Education Components

74HC153DW_2V	74HC160D_4V	74HC164N_6V	74HC175D_2V
74HC153DW_4V	74HC160D_6V	74HC165D_2V	74HC175D_4V
74HC153DW_6V	74HC160N_2V	74HC165D_4V	74HC175D_6V
74HC153N_2V	74HC160N_4V	74HC165D_6V	74HC175N_2V
74HC153N_4V	74HC160N_6V	74HC165N_2V	74HC175N_4V
74HC153N_6V	74HC161D_2V	74HC165N_4V	74HC175N_6V
74HC154DW_2V	74HC161D_4V	74HC165N_6V	74HC180D_2V
74HC154DW_4V	74HC161D_6V	74HC166D_2V	74HC180D_4V
74HC154DW_6V	74HC161N_2V	74HC166D_4V	74HC180D_6V
74HC154NT_2V	74HC161N_4V	74HC166D_6V	74HC180N_2V
74HC154NT_4V	74HC161N_6V	74HC166N_2V	74HC180N_4V
74HC154NT_6V	74HC162D_2V	74HC166N_4V	74HC180N_6V
74HC157D_2V	74HC162D_4V	74HC166N_6V	74HC190D_2V
74HC157D_4V	74HC162D_6V	74HC173D_2V	74HC190D_4V
74HC157D_6V	74HC162N_2V	74HC173D_4V	74HC190D_6V
74HC157N_2V	74HC162N_4V	74HC173D_6V	74HC190N_2V
74HC157N_4V	74HC162N_6V	74HC173N_2V	74HC190N_4V
74HC157N_6V	74HC163D_2V	74HC173N_4V	74HC190N_6V
74HC158D_2V	74HC163D_4V	74HC173N_6V	74HC191D_2V
74HC158D_4V	74HC163D_6V	74HC174D_2V	74HC191D_4V
74HC158D_6V	74HC163N_2V	74HC174D_4V	74HC191D_6V
74HC158N_2V	74HC163N_4V	74HC174D_6V	74HC191N_2V
74HC158N_4V	74HC163N_6V	74HC174N_2V	74HC191N_4V
74HC158N_6V	74HC164N_2V	74HC174N_4V	74HC191N_6V
74HC160D_2V	74HC164N_4V	74HC174N_6V	74HC192D_2V

Multisim 14.1 Education Components

74HC192D_4V	74HC21D_6V	74HC244DW_6V	74HC257N_2V
74HC192D_6V	74HC21N_2V	74HC244N_2V	74HC257N_4V
74HC192N_2V	74HC21N_4V	74HC244N_4V	74HC257N_6V
74HC192N_4V	74HC21N_6V	74HC244N_6V	74HC258D_2V
74HC192N_6V	74HC240DW_2V	74HC245DW_2V	74HC258D_4V
74HC193D_2V	74HC240DW_4V	74HC245DW_4V	74HC258D_6V
74HC193D_4V	74HC240DW_6V	74HC245DW_6V	74HC258N_2V
74HC193D_6V	74HC240N_2V	74HC245N_2V	74HC258N_4V
74HC193N_2V	74HC240N_4V	74HC245N_4V	74HC258N_6V
74HC193N_4V	74HC240N_6V	74HC245N_6V	74HC259D_2V
74HC193N_6V	74HC241DW_2V	74HC251D_2V	74HC259D_4V
74HC194N_2V	74HC241DW_4V	74HC251D_4V	74HC259D_6V
74HC194N_4V	74HC241DW_6V	74HC251D_6V	74HC259N_2V
74HC194N_6V	74HC241N_2V	74HC251N_2V	74HC259N_4V
74HC195N_2V	74HC241N_4V	74HC251N_4V	74HC259N_6V
74HC195N_4V	74HC241N_6V	74HC251N_6V	74HC266D_2V
74HC195N_6V	74HC242N_2V	74HC253D_2V	74HC266D_4V
74HC20D_2V	74HC242N_4V	74HC253D_4V	74HC266D_6V
74HC20D_4V	74HC242N_6V	74HC253D_6V	74HC266N_2V
74HC20D_6V	74HC243N_2V	74HC253N_2V	74HC266N_4V
74HC20N_2V	74HC243N_4V	74HC253N_4V	74HC266N_6V
74HC20N_4V	74HC243N_6V	74HC253N_6V	74HC273DW_2V
74HC20N_6V	74HC244_4V	74HC257D_2V	74HC273DW_4V
74HC21D_2V	74HC244DW_2V	74HC257D_4V	74HC273DW_6V
74HC21D_4V	74HC244DW_4V	74HC257D_6V	74HC273N_2V

Multisim 14.1 Education Components

74HC273N_4V	74HC30D_6V	74HC367N_2V	74HC374N_4V
74HC273N_6V	74HC30N_2V	74HC367N_4V	74HC374N_6V
74HC27D_2V	74HC30N_4V	74HC367N_6V	74HC375D_2V
74HC27D_4V	74HC30N_6V	74HC368D_2V	74HC375D_4V
74HC27D_6V	74HC32D_2V	74HC368D_4V	74HC375D_6V
74HC27N_2V	74HC32D_4V	74HC368D_6V	74HC375N_2V
74HC27N_4V	74HC32D_6V	74HC368N_2V	74HC375N_4V
74HC27N_6V	74HC32N_2V	74HC368N_4V	74HC375N_6V
74HC280D_2V	74HC32N_4V	74HC368N_6V	74HC377DW_2V
74HC280D_4V	74HC32N_6V	74HC36D_2V	74HC377DW_4V
74HC280D_6V	74HC365D_2V	74HC36D_4V	74HC377DW_6V
74HC280N_2V	74HC365D_4V	74HC36D_6V	74HC377N_2V
74HC280N_4V	74HC365D_6V	74HC36N_2V	74HC377N_4V
74HC280N_6V	74HC365N_2V	74HC36N_4V	74HC377N_6V
74HC283D_2V	74HC365N_4V	74HC36N_6V	74HC378D_2V
74HC283D_4V	74HC365N_6V	74HC373DW_2V	74HC378D_4V
74HC283D_6V	74HC366D_2V	74HC373DW_4V	74HC378D_6V
74HC283N_2V	74HC366D_4V	74HC373DW_6V	74HC378N_2V
74HC283N_4V	74HC366D_6V	74HC373N_2V	74HC378N_4V
74HC283N_6V	74HC366N_2V	74HC373N_4V	74HC378N_6V
74HC298N_2V	74HC366N_4V	74HC373N_6V	74HC379D_2V
74HC298N_4V	74HC366N_6V	74HC374DW_2V	74HC379D_4V
74HC298N_6V	74HC367D_2V	74HC374DW_4V	74HC379D_6V
74HC30D_2V	74HC367D_4V	74HC374DW_6V	74HC379J_2V
74HC30D_4V	74HC367D_6V	74HC374N_2V	74HC379J_4V

Multisim 14.1 Education Components

74HC379J_6V	74HC51D_2V	74HC76D_4V	74HC86D_6V
74HC379N_2V	74HC51D_4V	74HC76D_6V	74HC86N_2V
74HC379N_4V	74HC51D_6V	74HC76N_2V	74HC86N_4V
74HC379N_6V	74HC51N_2V	74HC76N_4V	74HC86N_6V
74HC386D_2V	74HC51N_4V	74HC76N_6V	74LS00D
74HC386D_4V	74HC51N_6V	74HC77D_2V	74LS00D
74HC386D_6V	74HC73D_2V	74HC77D_4V	74LS00N
74HC386N_2V	74HC73D_4V	74HC77D_6V	74LS00N
74HC386N_4V	74HC73D_6V	74HC77N_2V	74LS01D
74HC386N_6V	74HC73N_2V	74HC77N_4V	74LS01N
74HC390D_2V	74HC73N_4V	74HC77N_6V	74LS02D
74HC390D_4V	74HC73N_6V	74HC78D_2V	74LS02D
74HC390D_6V	74HC74D_2V	74HC78D_4V	74LS02N
74HC390N_2V	74HC74D_4V	74HC78D_6V	74LS02N
74HC390N_4V	74HC74D_6V	74HC78N_2V	74LS03D
74HC390N_6V	74HC74N_2V	74HC78N_4V	74LS03D
74HC393N_2V	74HC74N_4V	74HC78N_6V	74LS03N
74HC393N_4V	74HC74N_6V	74HC85AD_2V	74LS03N
74HC393N_6V	74HC75D_2V	74HC85AD_4V	74LS04D
74HC42D_2V	74HC75D_4V	74HC85AD_6V	74LS04D
74HC42D_4V	74HC75D_6V	74HC85AN_2V	74LS04N
74HC42D_6V	74HC75N_2V	74HC85AN_4V	74LS04N
74HC42N_2V	74HC75N_4V	74HC85AN_6V	74LS05D
74HC42N_4V	74HC75N_6V	74HC86D_2V	74LS05D
74HC42N_6V	74HC76D_2V	74HC86D_4V	74LS05N

Multisim 14.1 Education Components

74LS05N	74LS112N	74LS132D	74LS148D
74LS08D	74LS112N	74LS132N	74LS148D
74LS08D	74LS113D	74LS132N	74LS148N
74LS08J	74LS113D	74LS136D	74LS148N
74LS08J	74LS113N	74LS136N	74LS14D
74LS08N	74LS113N	74LS137D	74LS14D
74LS08N	74LS114D	74LS137N	74LS14N
74LS09D	74LS114D	74LS138D	74LS14N
74LS09D	74LS114N	74LS138D	74LS151D
74LS09N	74LS114N	74LS138N	74LS151D
74LS09N	74LS11D	74LS138N	74LS151N
74LS107D	74LS11D	74LS139D	74LS151N
74LS107D	74LS11N	74LS139D	74LS152J
74LS107N	74LS11N	74LS139N	74LS152N
74LS107N	74LS125D	74LS139N	74LS153D
74LS109D	74LS125D	74LS13D	74LS153D
74LS109D	74LS125N	74LS13N	74LS153N
74LS109N	74LS126D	74LS145D	74LS153N
74LS109N	74LS126D	74LS145D	74LS155D
74LS10D	74LS126N	74LS145N	74LS155D
74LS10D	74LS12D	74LS145N	74LS155N
74LS10N	74LS12D	74LS147D	74LS155N
74LS10N	74LS12N	74LS147D	74LS156D
74LS112D	74LS12N	74LS147N	74LS156D
74LS112D	74LS132D	74LS147N	74LS156N

Multisim 14.1 Education Components

74LS156N	74LS163N	74LS174N	74LS194D
74LS157D	74LS163N	74LS175D	74LS194D
74LS157D	74LS164D	74LS175D	74LS194N
74LS157N	74LS164D	74LS175N	74LS194N
74LS157N	74LS164N	74LS175N	74LS195D
74LS158D	74LS164N	74LS181DW	74LS195D
74LS158D	74LS165D	74LS181DW	74LS195N
74LS158N	74LS165D	74LS181N	74LS195N
74LS158N	74LS165N	74LS181N	74LS19AD
74LS15D	74LS165N	74LS183D	74LS19AN
74LS15D	74LS166D	74LS183N	74LS20D
74LS15N	74LS166D	74LS190D	74LS20D
74LS15N	74LS166N	74LS190D	74LS20N
74LS160D	74LS166N	74LS190N	74LS20N
74LS160D	74LS169D	74LS190N	74LS21D
74LS160N	74LS169D	74LS191D	74LS21D
74LS160N	74LS169N	74LS191D	74LS21N
74LS161D	74LS169N	74LS191N	74LS21N
74LS161N	74LS173D	74LS191N	74LS22D
74LS162D	74LS173D	74LS192D	74LS22D
74LS162D	74LS173N	74LS192D	74LS22N
74LS162N	74LS173N	74LS192N	74LS22N
74LS162N	74LS174D	74LS192N	74LS240DW
74LS163D	74LS174D	74LS193D	74LS240DW
74LS163D	74LS174N	74LS193N	74LS240N

Multisim 14.1 Education Components

74LS240N	74LS253D	74LS273N	74LS298D
74LS241DW	74LS253D	74LS279D	74LS298D
74LS241DW	74LS253N	74LS279N	74LS298N
74LS241N	74LS253N	74LS27D	74LS298N
74LS241N	74LS257D	74LS27D	74LS30D
74LS242D	74LS257D	74LS27N	74LS30N
74LS242N	74LS257N	74LS27N	74LS30N
74LS243D	74LS257N	74LS280D	74LS32D
74LS243N	74LS258D	74LS280D	74LS32D
74LS244DW	74LS258D	74LS280N	74LS32N
74LS244N	74LS258N	74LS280N	74LS32N
74LS245DW	74LS258N	74LS283D	74LS33D
74LS245N	74LS259D	74LS283N	74LS33D
74LS247D	74LS259N	74LS28D	74LS33N
74LS247N	74LS266D	74LS28D	74LS33N
74LS248D	74LS266D	74LS28N	74LS348D
74LS248N	74LS266N	74LS28N	74LS348N
74LS249J	74LS266N	74LS290D	74LS352D
74LS249N	74LS26D	74LS290D	74LS352D
74LS24AD	74LS26D	74LS290N	74LS352N
74LS24AN	74LS26N	74LS290N	74LS352N
74LS251D	74LS26N	74LS293D	74LS353D
74LS251D	74LS273DW	74LS293D	74LS353D
74LS251N	74LS273DW	74LS293N	74LS353N
74LS251N	74LS273N	74LS293N	74LS363D

Multisim 14.1 Education Components

74LS363N	74LS375D	74LS393D	74LS465N
74LS364D	74LS375N	74LS393D	74LS466DW
74LS364N	74LS377DW	74LS393N	74LS466DW
74LS365D	74LS377DW	74LS393N	74LS466N
74LS365D	74LS377N	74LS395D	74LS466N
74LS365N	74LS377N	74LS395D	74LS467DW
74LS365N	74LS378D	74LS395N	74LS467N
74LS366D	74LS378D	74LS395N	74LS468DW
74LS366N	74LS378N	74LS399D	74LS468N
74LS367D	74LS378N	74LS399N	74LS47D
74LS367D	74LS379D	74LS40D	74LS47D
74LS367N	74LS379D	74LS40D	74LS47N
74LS367N	74LS379N	74LS40N	74LS47N
74LS368D	74LS379N	74LS40N	74LS48D
74LS368D	74LS37D	74LS42D	74LS48D
74LS368N	74LS37D	74LS42D	74LS48N
74LS368N	74LS37N	74LS42N	74LS48N
74LS373DW	74LS386D	74LS42N	74LS49D
74LS373DW	74LS386N	74LS445D	74LS49N
74LS373N	74LS38D	74LS445D	74LS51D
74LS373N	74LS38D	74LS445N	74LS51D
74LS374DW	74LS38N	74LS445N	74LS51N
74LS374DW	74LS38N	74LS465DW	74LS51N
74LS374N	74LS390D	74LS465DW	74LS540DW
74LS374N	74LS390N	74LS465N	74LS540N

Multisim 14.1 Education Components

74LS541DW	74LS74N	74LS90N	74S08J
74LS541N	74LS75D	74LS90N	74S08N
74LS54D	74LS75D	74LS91D	74S09D
74LS54D	74LS75N	74LS91D	74S09N
74LS54N	74LS75N	74LS91N	74S10D
74LS54N	74LS76D	74LS91N	74S10N
74LS55D	74LS76D	74LS92D	74S112D
74LS55D	74LS76N	74LS92D	74S112N
74LS55N	74LS76N	74LS92N	74S113D
74LS55N	74LS77W	74LS92N	74S113N
74LS640DW	74LS77W	74LS93D	74S114D
74LS640N	74LS78D	74LS93D	74S114N
74LS645DW	74LS78D	74LS93N	74S11D
74LS645N	74LS78N	74LS93N	74S11N
74LS69D	74LS78N	74S00D	74S132D
74LS69D	74LS83D	74S00N	74S132N
74LS69N	74LS83N	74S02D	74S133D
74LS69N	74LS85D	74S02N	74S133N
74LS73D	74LS85N	74S03D	74S134D
74LS73D	74LS86D	74S03N	74S134D
74LS73N	74LS86D	74S04D	74S134N
74LS73N	74LS86N	74S04N	74S135D
74LS74D	74LS86N	74S05D	74S135N
74LS74D	74LS90D	74S05N	74S138D
74LS74N	74LS90D	74S08D	74S138N

Multisim 14.1 Education Components

74S139D	74S182N	74S283D	74S86N
74S139N	74S194D	74S283N	74STD06N
74S151D	74S194N	74S30D	74STD07N
74S151N	74S195D	74S30N	74STD116N
74S153D	74S195N	74S32D	74STD150N
74S153N	74S20D	74S32N	74STD154N
74S157D	74S20N	74S350D	74STD159N
74S157N	74S22D	74S350N	74STD16N
74S158D	74S22N	74S373DW	74STD17N
74S158N	74S240DW	74S373N	74STD198N
74S15D	74S240N	74S374DW	74STD199N
74S15N	74S241DW	74S374N	74STD25N
74S162D	74S241N	74S37D	74STD39N
74S162N	74S244DW	74S37N	74STD45N
74S163D	74S244N	74S38D	74STD72N
74S163N	74S251D	74S38N	75 kOhm [4114R-1-753]
74S169D	74S251N	74S40D	75 kOhm [4114R-1-753LF]
74S169N	74S253D	74S40N	75 kOhm [4608X-102-753LF]
74S174D	74S253N	74S51D	75 kOhm [4816P-1-753F]
74S174N	74S257D	74S51N	75 kOhm [4816P-2-753]
74S175D	74S257N	74S74D	75 kOhm [4816P-2-753LF]
74S175N	74S258D	74S74N	
74S181DW	74S258N	74S85D	
74S181N	74S280D	74S85N	
74S182D	74S280N	74S86D	

Multisim 14.1 Education Components

75 kOhm [CAY16-753J4LF]	75 kOhm [CRT0805-DY-7502ELF]	75 Ohm [4306R-101-750]	75 Ohm [4610X-101-750LF]
75 kOhm [CR0402-FX-7502GLF]	75 mF [C0805C759KGBGAC TU]	75 Ohm [4308H-101-750]	75 Ohm [4610X-102-750LF]
75 kOhm [CR0402-JW-753GLF]	75 mOhm [CRA2512-FZ-R075ELF]	75 Ohm [4308R-101-750]	75 Ohm [4613X-101-750LF]
75 kOhm [CR0603-FX-7502ELF]	75 mOhm [CRA2512-JZ-R075ELF]	75 Ohm [4308R-101-750LF]	75 Ohm [4816P-1-750]
75 kOhm [CR0603-JW-753ELF]	75 mOhm [CRM2512-FX-R075ELF]	75 Ohm [4308R-102-750]	75 Ohm [4816P-1-750LF]
75 kOhm [CR0805-FX-7502ELF]	75 mOhm [PWR163S-25-R075J]	75 Ohm [4308R-102-750LF]	75 Ohm [4816P-T01-750]
75 kOhm [CR0805-JW-753ELF]	75 mOhm [PWR163S-25-R075JE]	75 Ohm [4310R-101-750]	75 Ohm [CAT10-750J4LF]
75 kOhm [CR1206-FX-7502ELF]	75 mOhm [PWR220T-20-R075J]	75 Ohm [4310R-101-750LF]	75 Ohm [CAT16-750J2LF]
75 kOhm [CR1206-JW-753ELF]	75 mOhm [PWR221T-30-R075J]	75 Ohm [4416P-1-750]	75 Ohm [CAT16-750J4LF]
75 kOhm [CR1206-JW-753GLF]	75 Ohm [4114R-1-750]	75 Ohm [4604X-101-750LF]	75 Ohm [CAT16-75R0F4LF]
75 kOhm [CRM2512-FX-7502ELF]	75 Ohm [4116R-1-750]	75 Ohm [4605X-101-750LF]	75 Ohm [CAT25-750JALF]
75 kOhm [CRT0402-FZ-7502GLF]	75 Ohm [4116R-1-750]	75 Ohm [4606X-101-750LF]	75 Ohm [CAY10-750J2LF]
75 kOhm [CRT0603-FZ-7502ELF]	75 Ohm [4116R-1-750LF]	75 Ohm [4606X-102-750LF]	75 Ohm [CAY10-750J4LF]
75 kOhm [CRT0805-BW-7502ELF]	75 Ohm [4116R-1-750LF]	75 Ohm [4608X-101-750LF]	75 Ohm [CAY16-750J4LF]
		75 Ohm [4608X-102-750LF]	75 Ohm [CAY16-75R0F4LF]

Multisim 14.1 Education Components

75 Ohm [CAY17-750JALF]	75 Ohm [CRM1206-FX-75R0ELF]	75 Ohm [PWR221T-30-75R0J]	75 pF [C0805C750KBGAC TU]
75 Ohm [CR0402-FX-75R0GLF]	75 Ohm [CRM2512-FX-75R0ELF]	75 Ohm [PWR263S-20-75R0F]	75 pF [C0805C750KCGAC TU]
75 Ohm [CR0402-JW-750GLF]	75 Ohm [CRT0402-FZ-75R0GLF]	75 Ohm [PWR263S-20-75R0J]	75 pF [C1206C750K5GACT U]
75 Ohm [CR0603-FX-75R0ELF]	75 Ohm [CRT0805-BY-75R0ELF]	75 Ohm [PWR263S-35-75R0F]	75 pF [C1206C750KBGAC TU]
75 Ohm [CR0603-JW-750ELF]	75 Ohm [PWR163S-25-75R0F]	75 Ohm [PWR263S-35-75R0J]	75 pF [C1210C750KBGAC TU]
75 Ohm [CR0805-FX-75R0ELF]	75 Ohm [PWR163S-25-75R0FE]	75 Ohm [PWR3014W75R0JE]	75 pF [C1812C750KBGAC TU]
75 Ohm [CR0805-FX-75R0GLF]	75 Ohm [PWR163S-25-75R0J]	75 Ohm [PWR4318W75R0JE]	75 pF [C1825C750KBGAC TU]
75 Ohm [CR0805-JW-750ELF]	75 Ohm [PWR163S-25-75R0JE]	75 Ohm [PWR4525W75R0J]	75 pF [C2220C750KBGAC TU]
75 Ohm [CR1206-FX-75R0ELF]	75 Ohm [PWR220T-20-75R0F]	75 Ohm [PWR5322W75R0JE]	75 pF [C2225C750KBGAC TU]
75 Ohm [CR1206-JW-750ELF]	75 Ohm [PWR220T-20-75R0J]	75 Ohm [PWR6327W75R0J]	75 uH [SRR1205-750YL]
75 Ohm [CR2010-JW-750ELF]	75 Ohm [PWR220T-35-75R0J]	75 pF [C0603C750K5GACT U]	750 kOhm [4816P-1-754]
75 Ohm [CR2512-FX-75R0ELF]	75 Ohm [PWR221T-30-75R0F]	75 pF [C0805C750K2GACT U]	750 kOhm [CAY16-754J4LF]

Multisim 14.1 Education Components

750 kOhm [CHV0805-FX- 7503ELF]	750 mOhm [CRL0603-JW- R750ELF]	750 mOhm [PWR163S-25- R750J]	750 mOhm [PWR3014WR750JE]
750 kOhm [CR0402-FX- 7503GLF]	750 mOhm [CRL0805-FW- R750ELF]	750 mOhm [PWR1913WR750J]	750 mOhm [PWR4318WR750JE]
750 kOhm [CR0402-JW- 754GLF]	750 mOhm [CRL0805-JW- R750ELF]	750 mOhm [PWR1913WR750JE]	750 mOhm [PWR4525WR750F]
750 kOhm [CR0603-FX- 7503ELF]	750 mOhm [CRL1206-FW- R750ELF]	750 mOhm [PWR2010WR750JE]	750 mOhm [PWR4525WR750F E]
750 kOhm [CR0603-JW- 754ELF]	750 mOhm [CRL1206-JW- R750ELF]	750 mOhm [PWR220T-20- R750F]	750 mOhm [PWR4525WR750J]
750 kOhm [CR0805-FX- 7503ELF]	750 mOhm [CRL2010-FW- R750ELF]	750 mOhm [PWR220T-20- R750J]	750 mOhm [PWR4525WR750JE]
750 kOhm [CR0805-JW- 754ELF]	750 mOhm [CRL2010-JW- R750ELF]	750 mOhm [PWR2615WR750J]	750 mOhm [PWR5322WR750JE]
750 kOhm [CR1206-FX- 7503ELF]	750 mOhm [CRM2512-FX- R750ELF]	750 mOhm [PWR2615WR750JE]	750 mOhm [PWR6327WR750J]
750 kOhm [CR1206-JW- 754ELF]	750 mOhm [CRM2512-JX- R750ELF]	750 mOhm [PWR263S-20- R750F]	750 mOhm [PWR6327WR750JE]
750 kOhm [CRT0805-BY- 7503ELF]	750 mOhm [PWR163S-25- R750F]	750 mOhm [PWR263S-20- R750J]	750 nH [SRP1040- R75M]
750 mOhm [CRL0603-FW- R750ELF]	750 mOhm [PWR163S-25- R750FE]	750 mOhm [PWR263S-35- R750F]	750 nH [SRP1204- R50M]
		750 mOhm [PWR263S-35- R750J]	750 nH [SRP7028A- R75M]
			750 Ohm [4114R-1- 751]

Multisim 14.1 Education Components

750 Ohm [4114R-2-751]	750 Ohm [4610X-101-751LF]	750 Ohm [CR1206-JW-751ELF]	750 pF [C0402C751K3HACTU]
750 Ohm [4116R-1-751]	750 Ohm [4816P-1-751]	750 Ohm [CR2512-FX-7500ELF]	750 pF [C0402C751K5HACTU]
750 Ohm [4116R-1-751LF]	750 Ohm [4816P-1-751LF]	750 Ohm [CR2512-JW-751ELF]	750 pF [C0603C751K1HACTU]
750 Ohm [4116R-2-751]	750 Ohm [4816P-T01-751]	750 Ohm [CRM1206-FX-7500ELF]	750 pF [C0603C751K3HACTU]
750 Ohm [4306H-102-751]	750 Ohm [CAT16-7500F4LF]	750 Ohm [CRM2512-FX-7500ELF]	750 pF [C0603C751K5GACTU]
750 Ohm [4306R-102-751]	750 Ohm [CAT16-751J4LF]	750 Ohm [CRT0402-FZ-7500GLF]	750 pF [C0603C751K5HACTU]
750 Ohm [4308H-101-751]	750 Ohm [CAY16-7500F4LF]	750 Ohm [CRT0603-BY-7500ELF]	750 pF [C1210C751KBGAC TU]
750 Ohm [4308H-101-751LF]	750 Ohm [CAY16-751J4LF]	750 Ohm [CRT0603-FY-7500ELF]	750 pF [C1812C751KBGAC TU]
750 Ohm [4308R-102-751]	750 Ohm [CR0402-FX-7500GLF]	750 Ohm [PWR163S-25-7500FE]	750 pF [C1825C751KBGAC TU]
750 Ohm [4308R-102-751LF]	750 Ohm [CR0402-JW-751GLF]	750 Ohm [PWR263S-35-7500F]	750 pF [C2220C751KBGAC TU]
750 Ohm [4310R-101-751]	750 Ohm [CR0603-FX-7500ELF]	750 Ohm [PWR263S-35-7500FE]	750 pF [C2225C751KBGAC TU]
750 Ohm [4310R-101-751LF]	750 Ohm [CR0603-JW-751ELF]		
750 Ohm [4606X-101-751LF]	750 Ohm [CR0805-FX-7500ELF]		
750 Ohm [4608X-102-751LF]	750 Ohm [CR0805-JW-751ELF]		
750 Ohm [4609M-101-751LF]	750 Ohm [CR1206-FX-7500ELF]		

Multisim 14.1 Education Components

750 uOhm [CST0612-FC- R00075E]	76.8 Ohm [CR1206- FX-76R8ELF]	78.7 kOhm [CR0402-FX- 7872GLF]	787 kOhm [CR1206-FX- 7873ELF]
75LQ150	768 kOhm [CR0402-FX- 7683GLF]	78.7 kOhm [CR0603-FX- 7872ELF]	787 Ohm [CR0402- FX-7870GLF]
75SLQ030	768 kOhm [CR0603-FX- 7683ELF]	78.7 kOhm [CR0805-FX- 7872ELF]	787 Ohm [CR0603- FX-7870ELF]
75SLQ045	768 kOhm [CR0805-FX- 7683ELF]	78.7 kOhm [CR1206-FX- 7872ELF]	787 Ohm [CR0805- FX-7870ELF]
75SLQ060	768 kOhm [CR1206-FX- 7683ELF]	78.7 kOhm [CR1206-FX- 7872ELF]	787 Ohm [CR1206- FX-7870ELF]
76.8 kOhm [CR0201-FW- 7682GLF]	768 Ohm [CR0402- FX-7680GLF]	78.7 Ohm [CR0402- FX-78R7GLF]	7Line_Bussed
76.8 kOhm [CR0402-FX- 7682GLF]	768 Ohm [CR0603- FX-7680ELF]	78.7 Ohm [CR0603- FX-78R7ELF]	7Line_Isolated
76.8 kOhm [CR0603-FX- 7682GLF]	768 Ohm [CR0805- FX-7680ELF]	78.7 Ohm [CR0805- FX-78R7ELF]	7POS_ROTARY
76.8 kOhm [CR0805-FX- 7682ELF]	768 Ohm [CR1206- FX-7680ELF]	78.7 Ohm [CR1206- FX-78R7ELF]	8 kOhm [4116R-1- 802]
76.8 kOhm [CR1206-FX- 7682ELF]	768 Ohm [CRM2512-FX- 7680ELF]	781334-01	8 kOhm [4116R-1- 802LF]
76.8 Ohm [CR0603- FX-76R8ELF]	768 Ohm [CRT0402-BW- 7680GLF]	787 kOhm [CR0402-FX- 7873GLF]	8 kOhm [4816P- T02-802]
76.8 Ohm [CR0805- FX-76R8ELF]	777778-01	787 kOhm [CR0603-FX- 7873ELF]	8 kOhm [PWR4525W8001J]
76.8 Ohm [CR0805- FX-76R8GLF]	777779-01	787 kOhm [CR0805-FX- 7873ELF]	8 mOhm [CRE2512- FZ-R008E-2]
	779157-01		8 mOhm [CRE2512- FZ-R008E-3]
			8 mOhm [CRF2512- FX-R008ELF]

Multisim 14.1 Education Components

8 Ohm [4608M-102-8R0LF]	8.2 kOhm [4114R-1-822LF]	8.2 kOhm [4309R-101-822]	8.2 kOhm [4604X-102-822LF]
8 Ohm [PWR163S-25-8R00F]	8.2 kOhm [4114R-2-822]	8.2 kOhm [4309R-101-822LF]	8.2 kOhm [4605X-101-822LF]
8 Ohm [PWR163S-25-8R00FE]	8.2 kOhm [4116R-1-822]	8.2 kOhm [4310M-101-822]	8.2 kOhm [4606X-101-822LF]
8 Ohm [PWR220T-35-8R00F]	8.2 kOhm [4116R-1-822LF]	8.2 kOhm [4310M-101-822LF]	8.2 kOhm [4606X-102-822LF]
8 Ohm [PWR221T-30-8R00F]	8.2 kOhm [4116R-2-822]	8.2 kOhm [4310R-101-822]	8.2 kOhm [4607X-101-822LF]
8 Ohm [PWR263S-35-8R00F]	8.2 kOhm [4116R-2-822LF]	8.2 kOhm [4310R-101-822LF]	8.2 kOhm [4608H-102-822LF]
8.06 kOhm [CR0402-FX-8061GLF]	8.2 kOhm [4306R-101-822]	8.2 kOhm [4310R-102-822]	8.2 kOhm [4608M-101-822LF]
8.06 kOhm [CR0603-FX-8061ELF]	8.2 kOhm [4306R-101-822LF]	8.2 kOhm [4310R-102-822LF]	8.2 kOhm [4608X-101-822LF]
8.06 kOhm [CR0805-FX-8061ELF]	8.2 kOhm [4306R-102-822]	8.2 kOhm [4416P-1-822]	8.2 kOhm [4608X-102-822LF]
8.06 kOhm [CR1206-FX-8061ELF]	8.2 kOhm [4306R-102-822LF]	8.2 kOhm [4416P-1-822LF]	8.2 kOhm [4609X-101-822LF]
8.06 kOhm [CRT0603-BY-8061ELF]	8.2 kOhm [4308H-102-822LF]	8.2 kOhm [4416P-2-822LF]	8.2 kOhm [4610X-101-822LF]
8.06 kOhm [CRT0603-CY-8061ELF]	8.2 kOhm [4308R-101-822]	8.2 kOhm [4416P-T01-822]	8.2 kOhm [4610X-102-822LF]
8.2 kOhm [4114R-1-822]	8.2 kOhm [4308R-101-822LF]	8.2 kOhm [4416P-T01-822LF]	8.2 kOhm [4612X-102-822LF]
	8.2 kOhm [4308R-102-822]	8.2 kOhm [4420P-T01-822]	8.2 kOhm [4614X-102-822LF]
	8.2 kOhm [4308R-102-822LF]	8.2 kOhm [4604X-101-822LF]	8.2 kOhm [4814P-2-822]

Multisim 14.1 Education Components

8.2 kOhm [4814P-2-822LF]	8.2 kOhm [CAT16-822J4LF]	8.2 kOhm [CR1206-JW-822ELF]	8.2 mH [SRR1208-822KL]
8.2 kOhm [4814P-T02-822]	8.2 kOhm [CAT16-822J8LF]	8.2 kOhm [CR2010-JW-822ELF]	8.2 MOhm [4604X-102-825LF]
8.2 kOhm [4814P-T02-822LF]	8.2 kOhm [CAT25-822JALF]	8.2 kOhm [CR2512-JW-822ELF]	8.2 MOhm [CAT25-825JALF]
8.2 kOhm [4816P-1-822]	8.2 kOhm [CAY10-822J4LF]	8.2 kOhm [CRM1206-JW-822ELF]	8.2 MOhm [CR0603-JW-825ELF]
8.2 kOhm [4816P-1-822LF]	8.2 kOhm [CAY16-8201F4LF]	8.2 kOhm [CRM2512-JW-822ELF]	8.2 MOhm [CR0805-JW-825ELF]
8.2 kOhm [4816P-2-822]	8.2 kOhm [CAY16-822J4LF]	8.2 kOhm [CRT0603-BY-8201ELF]	8.2 MOhm [CR1206-JW-825ELF]
8.2 kOhm [4816P-2-822LF]	8.2 kOhm [CAY16-822J8LF]	8.2 kOhm [CRT0603-FY-8201ELF]	8.2 nF [C0402C822K3RACT U]
8.2 kOhm [4816P-T01-822]	8.2 kOhm [CAY17-822JALF]	8.2 kOhm [PWR163S-25-8201FE]	8.2 nF [C0402C822K4RACT U]
8.2 kOhm [4816P-T01-822LF]	8.2 kOhm [CR0402-FX-8201GLF]	8.2 mH [SDR0503-822JL]	8.2 nF [C0402C822K5RACT U]
8.2 kOhm [4816P-T02-822]	8.2 kOhm [CR0402-JW-822GLF]	8.2 mH [SDR0906-822KL]	8.2 nF [C0402C822K9RACT U]
8.2 kOhm [4816P-T02-822LF]	8.2 kOhm [CR0603-FX-8201ELF]	8.2 mH [SDR1005-822KL]	8.2 nF [C0603C822K1RACT U]
8.2 kOhm [4820P-2-822]	8.2 kOhm [CR0603-JW-822ELF]	8.2 mH [SRR0906-822YL]	8.2 nF [C0603C822K3GACT U]
8.2 kOhm [4820P-T02-822]	8.2 kOhm [CR0805-FX-8201ELF]	8.2 mH [SRR0908-822YL]	
8.2 kOhm [CAT10-822J4LF]	8.2 kOhm [CR0805-JW-822ELF]		
8.2 kOhm [CAT16-8201F4LF]	8.2 kOhm [CR1206-FX-8201ELF]		

Multisim 14.1 Education Components

8.2 nF [C0603C822K3HACT U]	8.2 nF [C0805C822K4RACT U]	8.2 nF [C1210C822K5GACT U]	8.2 nF [GMC7.3822K63K31 TR12]
8.2 nF [C0603C822K3RACT U]	8.2 nF [C0805C822K5GACT U]	8.2 nF [C1210C822K5RACT U]	8.2 nF [GMC7.3823K100K3 5TR12]
8.2 nF [C0603C822K4RACT U]	8.2 nF [C0805C822K5HACT U]	8.2 nF [C1210C822KARACT U]	8.2 nF [MMC5.7822K100J 31TR12]
8.2 nF [C0603C822K5RACT U]	8.2 nF [C0805C822K5RACT U]	8.2 nF [C1812C822K5GACT U]	8.2 nF [MMC5.7822K250J 31TR12]
8.2 nF [C0805C822K1GACT U]	8.2 nF [C1206C822K1HACT U]	8.2 nF [C1812C822K5RACT U]	8.2 nF [MMC5.7822K50J3 1TR12]
8.2 nF [C0805C822K1HACT U]	8.2 nF [C1206C822K1RACT U]	8.2 nF [C2220C822K2GACT U]	8.2 nF [MMC7.3822K100K 31TR12]
8.2 nF [C0805C822K1RACT U]	8.2 nF [C1206C822K2RACT U]	8.2 nF [GMC5.7822K100J3 1TR12]	8.2 nF [MMC7.3822K250K 31TR12]
8.2 nF [C0805C822K2RACT U]	8.2 nF [C1206C822K3HACT U]	8.2 nF [GMC5.7822K250J3 1TR12]	8.2 nF [MMC7.3822K400K 33TR12]
8.2 nF [C0805C822K3GACT U]	8.2 nF [C1206C822K5HACT U]	8.2 nF [GMC5.7822K50J31 TR12]	8.2 nF [MMC7.3822K50K3 1TR12]
8.2 nF [C0805C822K3HACT U]	8.2 nF [C1206C822K5RACT U]	8.2 nF [GMC7.3822K100K3 1TR12]	8.2 nF [MMC7.3822K63K3 1TR12]
8.2 nF [C0805C822K3RACT U]	8.2 nF [C1206C822KARACT U]	8.2 nF [GMC7.3822K400K3 5TR12]	8.2 Ohm [CR0402- J/-8R2GLF] 8.2 Ohm [CR0603- J/-8R2ELF]

Multisim 14.1 Education Components

8.2 Ohm [CR0805-J/-8R2ELF]	8.2 Ohm [FW20A8R20JA]	8.2 uF [20TQC8R2M]	8.2 uF [MDC10825K50A57P8TUBE]
8.2 Ohm [CR1206-J/-8R2ELF]	8.2 Ohm [FW30A8R20JA]	8.2 uF [A700V825M016AT E045]	8.2 uH [SDE0403A-8R2M]
8.2 Ohm [CR1206-JW-8R2ELF]	8.2 Ohm [PWR163S-25-8R20F]	8.2 uF [C1206C825K4PACT U]	8.2 uH [SDE0604A-8R2M]
8.2 Ohm [CR2512-J/-8R2ELF]	8.2 Ohm [PWR163S-25-8R20J]	8.2 uF [C1206C825K8PACT U]	8.2 uH [SDE0805A-8R2M]
8.2 Ohm [CRL0603-FW-8R20ELF]	8.2 Ohm [PWR220T-20-8R20F]	8.2 uF [C1206C825K8RACT U]	8.2 uH [SDE1006A-8R2M]
8.2 Ohm [CRL0603-JW-8R20ELF]	8.2 Ohm [PWR220T-20-8R20J]	8.2 uF [C1206C825K9RACT U]	8.2 uH [SDR0302-8R2ML]
8.2 Ohm [CRL0805-FW-8R20ELF]	8.2 Ohm [PWR221T-30-8R20F]	8.2 uF [C1210C825K3PACT U]	8.2 uH [SDR0403-8R2ML]
8.2 Ohm [CRL0805-JW-8R20ELF]	8.2 Ohm [PWR221T-30-8R20J]	8.2 uF [C1210C825K4PACT U]	8.2 uH [SDR0604-8R2ML]
8.2 Ohm [CRL1206-FW-8R20ELF]	8.2 Ohm [PWR263S-20-8R20F]	8.2 uF [MDC10825K100A58P7TUBE]	8.2 uH [SDR0703-8R2ML]
8.2 Ohm [CRL1206-JW-8R20ELF]	8.2 Ohm [PWR263S-20-8R20FE]	8.2 uF [MDC10825K100A58P8TUBE]	8.2 uH [SDR0906-8R2ML]
8.2 Ohm [CRL2010-FW-8R20ELF]	8.2 Ohm [PWR263S-20-8R20J]	8.2 uF [MDC10825K50A57P7TUBE]	8.2 uH [SDR1006-8R2ML]
8.2 Ohm [CRL2010-JW-8R20ELF]	8.2 Ohm [PWR263S-35-8R20F]		8.2 uH [SDR1307-8R2ML]
8.2 Ohm [CRL2512-FW-8R20ELF]			8.2 uH [SDR1307A-8R2M]
8.2 Ohm [CRM2512-JW-8R2ELF]			8.2 uH [SDR1806-8R2ML]
8.2 Ohm [FW10A8R20JA]			8.2 uH [SDR6603-8R2M]

Multisim 14.1 Education Components

8.2 uH [SRN5040-8R2M]	8.2 uH [SRP7050TA-8R2M]	8.2 uH [SRU1028-8R2Y]	8.25 kOhm [CRM0805-FX-8251ELF]
8.2 uH [SRN6045-8R2Y]	8.2 uH [SRR0805-8R2M]	8.2 uH [SRU1028A-8R2Y]	8.25 kOhm [CRT0603-DW-8251ELF]
8.2 uH [SRN8040-8R2Y]	8.2 uH [SRR0906-8R2ML]	8.2 uH [SRU1038-8R2Y]	8.25 kOhm [CRT0805-CX-8251ELF]
8.2 uH [SRP1038A-8R2M]	8.2 uH [SRR1210-8R2Y]	8.2 uH [SRU1048-8R2Y]	8.25 Ohm [CRM1206-FX-8R25ELF]
8.2 uH [SRP1040-8R2M]	8.2 uH [SRR1210A-8R2Y]	8.2 uH [SRU1048A-8R2Y]	8.45 kOhm [CR0402-FX-8451GLF]
8.2 uH [SRP1235-8R2M]	8.2 uH [SRR1240-8R2M]	8.2 uH [SRU6025-8R2Y]	8.45 kOhm [CR0603-FX-8451ELF]
8.2 uH [SRP1265A-8R2M]	8.2 uH [SRR1260-8R2Y]	8.2 uH [SRU6025A-8R2Y]	8.45 kOhm [CR0805-FX-8451ELF]
8.2 uH [SRP1270-8R2M]	8.2 uH [SRR1260A-8R2Y]	8.2 uH [SRU8028-8R2Y]	8.45 kOhm [CR1206-FX-8451ELF]
8.2 uH [SRP1770TA-8R2M]	8.2 uH [SRR1280-8R2Y]	8.25 kOhm [CAY16-8251F4LF]	8.45 kOhm [CR1206-FX-8451ELF]
8.2 uH [SRP4012TA-8R2M]	8.2 uH [SRR4011-8R2YL]	8.25 kOhm [CR0402-FX-8251GLF]	8.45 kOhm [CRT0603-BW-8451ELF]
8.2 uH [SRP4020TA-8R2M]	8.2 uH [SRR4018-8R2Y]	8.25 kOhm [CR0603-FX-8251ELF]	8.6 uH [SRR6028-8R6Y]
8.2 uH [SRP5015TA-8R2M]	8.2 uH [SRR4028-8R2Y]	8.25 kOhm [CR0805-FX-8251ELF]	8.66 kOhm [CR0402-FX-8661GLF]
8.2 uH [SRP6540-8R2M]	8.2 uH [SRR5028-8R2Y]	8.25 kOhm [CR1206-FX-8251ELF]	
8.2 uH [SRP7028A-8R2M]	8.2 uH [SRR6038-8R2Y]		
8.2 uH [SRP7030-8R2FM]	8.2 uH [SRR6040A-8R2Y]		

Multisim 14.1 Education Components

8.66 kOhm [CR0603-FX-8661ELF]	80 kOhm [4309R-101-803]	80.6 Ohm [CR1206-FX-80R6ELF]	806 Ohm [CR0402-FX-8060GLF]
8.66 kOhm [CR0805-FX-8661ELF]	80 mOhm [CRA2512-FZ-R080ELF]	80.6 Ohm [CRT0402-BY-80R6GLF]	806 Ohm [CR0603-FX-8060ELF]
8.66 kOhm [CR1206-FX-8661ELF]	80 mOhm [CRA2512-JZ-R080ELF]	80.6 Ohm [CRT0805-BY-80R6ELF]	806 Ohm [CR0805-FX-8060ELF]
8.66 kOhm [CRT0603-DX-8661ELF]	80 mOhm [PWR4412-2SCR0800F]	80.6 Ohm [PWR5322W80R6F E]	806 Ohm [CRT0603-DY-8060ELF]
8.7 uH [SRR6038-8R7Y]	80 mOhm [PWR4412-2SCR0800J]	800 nH [SRP1040-R80M]	806 Ohm [CRT1206-BY-8060ELF]
8.87 kOhm [CR0402-FX-8871GLF]	80.6 kOhm [CR0402-FX-8062GLF]	800 nH [SRP1045-R80M]	80CLQ150
8.87 kOhm [CR0603-FX-8871ELF]	80.6 kOhm [CR0603-FX-8062ELF]	800 nH [SRU1048-R80Y]	80SCLQ030
8.87 kOhm [CR0603-FX-8871GLF]	80.6 kOhm [CR0805-FX-8062ELF]	8051	80SCLQ060
8.87 kOhm [CR0805-FX-8871ELF]	80.6 kOhm [CR1206-FX-8062ELF]	8052	80SQ045NG
8.87 kOhm [CR1206-FX-8871ELF]	80.6 Ohm [CR0402-FX-80R6GLF]	806 kOhm [CR0402-FX-8063GLF]	80SQ045NRLG
8.87 kOhm [CR0603-FX-8871GLF]	80.6 Ohm [CR0603-FX-80R6ELF]	806 kOhm [CR0603-FX-8063ELF]	82 kOhm [4114R-1-823]
8.87 kOhm [CR0805-FX-8871ELF]	80.6 Ohm [CR0805-FX-80R6ELF]	806 kOhm [CR1206-FX-8063ELF]	82 kOhm [4114R-1-823LF]
8.87 kOhm [CR1206-FX-8871ELF]	80.6 Ohm [CR0805-FX-80R6ELF]	806 kOhm [CR0805-FX-8063ELF]	82 kOhm [4114R-2-823]
8.9 uH [SRR5018-8R9Y]			82 kOhm [4116R-1-823]

Multisim 14.1 Education Components

82 kOhm [4116R-2-823]	82 kOhm [4310R-102-823]	82 kOhm [4608X-102-823LF]	82 kOhm [CAT25-823JALF]
82 kOhm [4116R-2-823LF]	82 kOhm [4310R-102-823LF]	82 kOhm [4609X-101-823LF]	82 kOhm [CAY16-8202F4LF]
82 kOhm [4306M-102-823LF]	82 kOhm [4416P-1-823]	82 kOhm [4610X-101-823LF]	82 kOhm [CAY16-823J4LF]
82 kOhm [4306R-101-823]	82 kOhm [4416P-T01-823]	82 kOhm [4610X-102-823LF]	82 kOhm [CAY16-823J8LF]
82 kOhm [4306R-101-823LF]	82 kOhm [4420P-1-823]	82 kOhm [4611X-101-823LF]	82 kOhm [CR0201-FW-8202GLF]
82 kOhm [4306R-102-823]	82 kOhm [4420P-1-823LF]	82 kOhm [4614X-102-823LF]	82 kOhm [CR0402-FX-8202GLF]
82 kOhm [4306R-102-823LF]	82 kOhm [4420P-2-823]	82 kOhm [4816P-1-823]	82 kOhm [CR0402-JW-823GLF]
82 kOhm [4308H-102-823]	82 kOhm [4420P-T01-823]	82 kOhm [4816P-1-823LF]	82 kOhm [CR0603-FX-8202ELF]
82 kOhm [4308H-102-823LF]	82 kOhm [4420P-T02-823]	82 kOhm [4816P-2-823]	82 kOhm [CR0603-JW-823ELF]
82 kOhm [4308R-101-823]	82 kOhm [4604X-102-823LF]	82 kOhm [4816P-2-823LF]	82 kOhm [CR0805-FX-8202ELF]
82 kOhm [4308R-101-823LF]	82 kOhm [4605X-101-823LF]	82 kOhm [4816P-T01-823]	82 kOhm [CR0805-FX-8202GLF]
82 kOhm [4308R-102-823]	82 kOhm [4606X-101-823LF]	82 kOhm [4816P-T01-823LF]	82 kOhm [CR0805-JW-823ELF]
82 kOhm [4308R-102-823LF]	82 kOhm [4606X-102-823LF]	82 kOhm [4816P-T02-823]	82 kOhm [CR1206-FX-8202ELF]
82 kOhm [4310R-101-823]	82 kOhm [4608H-102-823LF]	82 kOhm [4816P-T02-823LF]	82 kOhm [CR1206-JW-823ELF]
82 kOhm [4310R-101-823LF]	82 kOhm [4608X-101-823LF]	82 kOhm [CAT16-823J4LF]	82 kOhm [CR1206-JW-823GLF]

Multisim 14.1 Education Components

82 kOhm [CRM2512-JW-823ELF]	82 mOhm [PWR4525WR082JE]	82 nF [C0805C823K5RACTU]	82 nF [C1206C823K5RACTU]
82 kOhm [PWR263S-20-8202F]	82 nF [C0402C823K4RACTU]	82 nF [C0805C823K8RACTU]	82 nF [C1206C823K8RACTU]
82 kOhm [PWR263S-20-8202FE]	82 nF [C0402C823K8RACTU]	82 nF [C0805C823M5UAC TU]	82 nF [C1206C823M5UAC TU]
82 kOhm [PWR263S-20-8202J]	82 nF [C0402C823K9RACTU]	82 nF [C0805F823K3RACTU]	82 nF [C1206F823K1RACTU]
82 mF [C0603C829K2GACTU]	82 nF [C0603C823K3RACTU]	82 nF [C0805F823K4RACTU]	82 nF [C1206F823K3RACTU]
82 mF [C0805C829K5GACTU]	82 nF [C0603C823K4RACTU]	82 nF [C0805F823K5RACTU]	82 nF [C1206F823K4RACTU]
82 mF [C0805C829KBGAC TU]	82 nF [C0603C823K5RACTU]	82 nF [C1206C823K1RACTU]	82 nF [C1206F823K5RACTU]
82 mOhm [CRL1206-JW-R082ELF]	82 nF [C0603C823K8RACTU]	82 nF [C1206C823K2RACTU]	82 nF [C1210C823K1GACTU]
82 mOhm [CRM1206-FX-R082ELF]	82 nF [C0805C823K1RACTU]	82 nF [C1206C823K3HACTU]	82 nF [C1210C823K1HACTU]
82 mOhm [CRM2010-FX-R082ELF]	82 nF [C0805C823K3RACTU]	82 nF [C1206C823K3RACTU]	82 nF [C1210C823K1RACTU]
82 mOhm [PWR4525NR082JE]	82 nF [C0805C823K4RACTU]	82 nF [C1206C823K5HACTU]	82 nF [C1210C823K3HACTU]

Multisim 14.1 Education Components

82 nF [C1210C823K5GACT U]	82 nF [C2220C823K1GACT U]	82 nF [MDC10823K630A5 8P8TUBE]	82 nF [MDS15823K50B53 P3TUBE]
82 nF [C1210C823K5HACT U]	82 nF [C2220C823K2GACT U]	82 nF [MDC15823K100B5 3P3TUBE]	82 nF [MDS15823K630B5 3P3TUBE]
82 nF [C1210C823K5RACT U]	82 nF [C2220C823K5GACT U]	82 nF [MDC15823K250B5 3P3TUBE]	82 Ohm [4114R-1- 820]
82 nF [C1210C823KARACT U]	82 nF [GMC5.7823K50J31 TR12]	82 nF [MDC15823K400B5 3P3TUBE]	82 Ohm [4114R-1- 820LF]
82 nF [C1210C823M1UAC TU]	82 nF [GMC7.3822K250K3 1TR12]	82 nF [MDC15823K50B53 P3TUBE]	82 Ohm [4114R-2- 820]
82 nF [C1210F823K2RACT U]	82 nF [GMC7.3823K63K31 TR12]	82 nF [MDC15823K630B5 3P3TUBE]	82 Ohm [4116R-1- 820]
82 nF [C1812C823K1GACT U]	82 nF [MDC10823K100A5 2P3TUBE]	82 nF [MDK10823K630A5 8P7TUBE]	82 Ohm [4116R-1- 820LF]
82 nF [C1812C823K1HACT U]	82 nF [MDC10823K250A5 2P3TUBE]	82 nF [MDK10823K630A5 8P8TUBE]	82 Ohm [4116R-2- 820]
82 nF [C1812C823K5GACT U]	82 nF [MDC10823K400A5 2P3TUBE]	82 nF [MDK15823K400B5 3P3TUBE]	82 Ohm [4116R-2- 820LF]
82 nF [C1812C823K5HACT U]	82 nF [MDC10823K50A52 P3TUBE]	82 nF [MDK15823K50B53 P3TUBE]	82 Ohm [4306M- 102-820]
82 nF [C1812C823K5RACT U]	82 nF [MDC10823K630A5 8P7TUBE]	82 nF [MDS15823K400B5 3P3TUBE]	82 Ohm [4306M- 102-820LF]
			82 Ohm [4306R- 101-820]
			82 Ohm [4306R- 101-820LF]
			82 Ohm [4306R- 102-820]
			82 Ohm [4308H- 101-820]

Multisim 14.1 Education Components

82 Ohm [4308R-101-820]	82 Ohm [4420P-1-820]	82 Ohm [4610X-101-820LF]	82 Ohm [4820P-T01-820]
82 Ohm [4308R-101-820LF]	82 Ohm [4420P-2-820]	82 Ohm [4610X-102-820LF]	82 Ohm [CAT10-820J4LF]
82 Ohm [4308R-102-820]	82 Ohm [4420P-T01-820]	82 Ohm [4814P-2-820]	82 Ohm [CAT16-820J4LF]
82 Ohm [4308R-102-820LF]	82 Ohm [4420P-T02-820]	82 Ohm [4814P-2-820LF]	82 Ohm [CAT16-82R0F4LF]
82 Ohm [4309R-101-820]	82 Ohm [4604X-101-820LF]	82 Ohm [4814P-T02-820]	82 Ohm [CAT25-820JALF]
82 Ohm [4310H-101-820]	82 Ohm [4604X-102-820LF]	82 Ohm [4814P-T02-820LF]	82 Ohm [CAY10-820J4LF]
82 Ohm [4310H-101-820LF]	82 Ohm [4605X-101-820LF]	82 Ohm [4816P-1-820]	82 Ohm [CAY16-820J4LF]
82 Ohm [4310R-101-820]	82 Ohm [4606X-101-820LF]	82 Ohm [4816P-1-820LF]	82 Ohm [CAY16-820J8LF]
82 Ohm [4310R-101-820LF]	82 Ohm [4606X-102-820LF]	82 Ohm [4816P-2-820]	82 Ohm [CAY16-82R0F4LF]
82 Ohm [4310R-102-820]	82 Ohm [4607X-101-820LF]	82 Ohm [4816P-2-820LF]	82 Ohm [CR0201-JW-820GLF]
82 Ohm [4310R-102-820LF]	82 Ohm [4608H-101-820LF]	82 Ohm [4816P-T01-820]	82 Ohm [CR0402-FX-82R0GLF]
82 Ohm [4416P-1-820]	82 Ohm [4608X-101-820LF]	82 Ohm [4816P-T01-820LF]	82 Ohm [CR0402-JW-820GLF]
82 Ohm [4416P-2-820]	82 Ohm [4608X-102-820LF]	82 Ohm [4816P-T02-820]	82 Ohm [CR0603-FX-82R0ELF]
82 Ohm [4416P-T01-820]	82 Ohm [4609X-101-820LF]	82 Ohm [4816P-T02-820LF]	82 Ohm [CR0603-JW-820ELF]
82 Ohm [4416P-T02-820]	82 Ohm [4610H-101-820LF]	82 Ohm [4818P-2-820]	82 Ohm [CR0805-FX-82R0ELF]

Multisim 14.1 Education Components

82 Ohm [CR0805-FX-82R0GLF]	82 Ohm [PWR220T-20-82R0F]	82 pF [C0805C820KBGAC TU]	82 pF [CA064C820K2GAC TU]
82 Ohm [CR0805-JW-820ELF]	82 Ohm [PWR263S-35-82R0FE]	82 pF [C1206C820K1GACT U]	82 pF [CDR31BP820BKSM]]
82 Ohm [CR1206-FX-82R0ELF]	82 Ohm [PWR4318W82R0JE]]	82 pF [C1206C820K2GACT U]	82 uF [A700V826M004AT E018]
82 Ohm [CR2010-JW-820ELF]	82 pF [C0201C820K3GACT U]	82 pF [C1206C820K5GACT U]	82 uF [A700V826M004AT E025]
82 Ohm [CR2512-FX-82R0ELF]	82 pF [C0402C820K3GACT U]	82 pF [C1206C820KBGAC TU]	82 uF [A700V826M004AT E028]
82 Ohm [CRM1206-JW-820ELF]	82 pF [C0402C820K5GACT U]	82 pF [C1206C820KCGAC TU]	82 uF [A700V826M006AT E018]
82 Ohm [CRM2512-JW-820ELF]	82 pF [C0603C820K5GACT U]	82 pF [C1210C820KBGAC TU]	82 uF [A700V826M006AT E025]
82 Ohm [FW10A82R0JA]	82 pF [C0805C820K1GACT U]	82 pF [C1812C820KBGAC TU]	82 uF [A700V826M006AT E028]
82 Ohm [FW20A82R0JA]	82 pF [C0805C820K2GACT U]	82 pF [C1825C820KBGAC TU]	82 uF [A700V826M2R5AT E018]
82 Ohm [FW30A82R0JA]	82 pF [C0805C820K3GACT U]	82 pF [C2220C820KBGAC TU]	82 uF [A700V826M2R5AT E025]
82 Ohm [FW50A82R0JA]	82 pF [C0805C820K5GACT U]	82 pF [C2225C820KBGAC TU]	82 uF [A700V826M2R5AT E028]

Multisim 14.1 Education Components

82 uF [EEFSX0G820ER]	82 uH [SDR1105- 820KL]	82 uH [SRR1210- 820M]	82 uH [SRU1028- 820Y]
82 uF [T520C826M008AT E025]	82 uH [SDR1307- 820KL]	82 uH [SRR1210A- 820M]	82 uH [SRU1028A- 820Y]
82 uF [T520C826M008AT E045]	82 uH [SDR1307A- 820K]	82 uH [SRR1240- 820M]	82 uH [SRU1048- 820Y]
82 uH [SDE0604A- 820K]	82 uH [SDR6603- 820M]	82 uH [SRR1260- 820M]	82 uH [SRU1048A- 820Y]
82 uH [SDE0805A- 820K]	82 uH [SRR0735A- 820M]	82 uH [SRR1260A- 820M]	82.5 kOhm [CR0402-FX- 8252GLF]
82 uH [SDE1006A- 820K]	82 uH [SRR0745A- 820M]	82 uH [SRR1280- 820M]	82.5 kOhm [CR0603-FX- 8252ELF]
82 uH [SDR0302- 820KL]	82 uH [SRR0804- 820K]	82 uH [SRR4011- 820YL]	82.5 kOhm [CR0805-FX- 8252ELF]
82 uH [SDR0403- 820KL]	82 uH [SRR0805- 820K]	82 uH [SRR4018- 820Y]	82.5 kOhm [CR1206-FX- 8252ELF]
82 uH [SDR0503- 820KL]	82 uH [SRR0905- 820Y]	82 uH [SRR4028- 820Y]	82.5 kOhm [CRT0402-BY- 8252GLF]
82 uH [SDR0603- 820KL]	82 uH [SRR0906- 820ML]	82 uH [SRR5018- 820Y]	82.5 kOhm [CRT0402-FZ- 8252GLF]
82 uH [SDR0604- 820KL]	82 uH [SRR0908- 820ML]	82 uH [SRR5028- 820Y]	82.5 kOhm [CRT0603-BY- 8252ELF]
82 uH [SDR0703- 820KL]	82 uH [SRR1003- 820M]	82 uH [SRR6028- 820Y]	82.5 kOhm [CRT0603-FZ- 8252ELF]
82 uH [SDR0805- 820KL]	82 uH [SRR1005- 820Y]	82 uH [SRR6038- 820Y]	82.5 kOhm [CRT1206-FZ- 8252ELF]
82 uH [SDR0906- 820KL]	82 uH [SRR1206- 820YL]	82 uH [SRR6040A- 820M]	
82 uH [SDR1006- 820KL]	82 uH [SRR1208- 820YL]	82 uH [SRR7045- 820M]	

Multisim 14.1 Education Components

82.5 Ohm [CAY16-82R5F4LF]	820 kOhm [4308R-102-824]	820 kOhm [4816P-T01-824LF]	820 kOhm [CR1206-JW-824ELF]
82.5 Ohm [CR0402-FX-82R5GLF]	820 kOhm [4308R-102-824LF]	820 kOhm [4816P-T02-824]	820 kOhm [CR2010-JW-824ELF]
82.5 Ohm [CR0603-FX-82R5ELF]	820 kOhm [4310R-102-824]	820 kOhm [4816P-T02-824LF]	820 kOhm [CRM2010-FX-8203ELF]
82.5 Ohm [CR0805-FX-82R5ELF]	820 kOhm [4605X-101-824LF]	820 kOhm [CAT16-824J4LF]	820 mOhm [CR1206-J/-R82ELF]
82.5 Ohm [CR1206-FX-82R5ELF]	820 kOhm [4606X-101-824LF]	820 kOhm [CAT25-824JALF]	820 mOhm [CRL0603-FW-R820ELF]
82.5 Ohm [CR2512-FX-82R5ELF]	820 kOhm [4606X-102-824LF]	820 kOhm [CAY16-824J4LF]	820 mOhm [CRL0603-JW-R820ELF]
82.5 Ohm [CRM1206-FX-82R5ELF]	820 kOhm [4608X-101-824LF]	820 kOhm [CAY16-824J8LF]	820 mOhm [CRL0805-FW-R820ELF]
82.5 Ohm [CRT0402-FZ-82R5GLF]	820 kOhm [4608X-102-824LF]	820 kOhm [CR0402-FX-8203GLF]	820 mOhm [CRL0805-JW-R820ELF]
82.5 Ohm [CRT0805-CX-82R5ELF]	820 kOhm [4608X-AP2-824LF]	820 kOhm [CR0603-FX-8203ELF]	820 mOhm [CRL1206-FW-R820ELF]
820 kOhm [4114R-1-824]	820 kOhm [4609X-101-824LF]	820 kOhm [CR0603-JW-824ELF]	820 mOhm [CRL1206-JW-R820ELF]
820 kOhm [4114R-1-824LF]	820 kOhm [4610X-101-824LF]	820 kOhm [CR0805-FX-8203ELF]	820 mOhm [CRL2010-FW-R820ELF]
820 kOhm [4116R-1-824]	820 kOhm [4610X-102-824LF]	820 kOhm [CR0805-JW-824ELF]	
820 kOhm [4116R-1-824LF]	820 kOhm [4816P-1-824]	820 kOhm [CR1206-FX-8203ELF]	
820 kOhm [4306R-102-824]	820 kOhm [4816P-1-824LF]		

Multisim 14.1 Education Components

820 mOhm [CRL2010-JW- R820ELF]	820 nF [C1206C824K4RACT U]	820 nF [C1825C824KARACT U]	820 nF [MDC15824K50B53 P3TUBE]
820 mOhm [CRL2512-FW- R820ELF]	820 nF [C1206F824K4RACT U]	820 nF [C2220C824K1RACT U]	820 nF [MDK15824K100B5 3P3TUBE]
820 mOhm [CRL2512-JW- R820ELF]	820 nF [C1210C824K5RACT U]	820 nF [C2220C824K5RACT U]	820 nF [MDK15824K50B53 P3TUBE]
820 mOhm [CRM1206-FX- R820ELF]	820 nF [C1210C824K8RACT U]	820 nF [C2220C824KARACT U]	820 nF [MMC10.2824K63A 31TR16]
820 mOhm [CRM2010-FX- R820ELF]	820 nF [C1210F824K3RACT U]	820 nF [C2225C824K5RACT U]	820 nH [SRN4018- R82Y]
820 mOhm [CRM2512-FX- R820ELF]	820 nF [C1210F824K4RACT U]	820 nF [C2225C824KARACT U]	820 nH [SRP1235- R82M]
820 mOhm [CRM2512-JX- R820ELF]	820 nF [C1812C824K5RACT U]	820 nF [MDC10824K100A5 2P3TUBE]	820 nH [SRP1250- R82M]
820 nF [C0603C824K8PACT U]	820 nF [C1812C824M5UAC TU]	820 nF [MDC10824K250A5 7P7TUBE]	820 nH [SRP1265A- R82M]
820 nF [C0805C824K4RACT U]	820 nF [C1812F824K1RACT U]	820 nF [MDC10824K250A5 7P8TUBE]	820 nH [SRP6540- R82M]
820 nF [C0805C824K8RACT U]	820 nF [C1812F824K3RACT U]	820 nF [MDC10824K50A52 P3TUBE]	820 nH [SRP7028A- R82M]
820 nF [C1206C824K3RACT U]	820 nF [C1812F824K5RACT U]	820 nF [MDC15824K100B5 3P3TUBE]	820 nH [SRP7030- R82FM]
			820 nH [SRP7050TA-R82M]
			820 Ohm [4114R-1- 821]
			820 Ohm [4114R-1- 821LF]

Multisim 14.1 Education Components

820 Ohm [4114R-2-821]	820 Ohm [4308R-101-821LF]	820 Ohm [4606X-101-821LF]	820 Ohm [4612X-102-821LF]
820 Ohm [4116R-1-821]	820 Ohm [4308R-102-821]	820 Ohm [4606X-102-821LF]	820 Ohm [4814P-2-821]
820 Ohm [4116R-1-821LF]	820 Ohm [4308R-102-821LF]	820 Ohm [4607X-101-821LF]	820 Ohm [4814P-T02-821]
820 Ohm [4116R-2-821]	820 Ohm [4309R-101-821]	820 Ohm [4608H-101-821LF]	820 Ohm [4816P-1-821]
820 Ohm [4116R-2-821LF]	820 Ohm [4309R-101-821LF]	820 Ohm [4608M-102-821LF]	820 Ohm [4816P-1-821LF]
820 Ohm [4306H-101-821]	820 Ohm [4310R-101-821]	820 Ohm [4608X-101-821LF]	820 Ohm [4816P-2-821]
820 Ohm [4306H-101-821LF]	820 Ohm [4310R-101-821LF]	820 Ohm [4608X-102-821LF]	820 Ohm [4816P-2-821LF]
820 Ohm [4306R-101-821]	820 Ohm [4310R-102-821]	820 Ohm [4608X-AP1-821LF]	820 Ohm [4816P-T01-821]
820 Ohm [4306R-101-821LF]	820 Ohm [4310R-102-821LF]	820 Ohm [4609H-101-821LF]	820 Ohm [4816P-T01-821LF]
820 Ohm [4306R-102-821]	820 Ohm [4311R-101-821]	820 Ohm [4609X-101-821LF]	820 Ohm [4816P-T02-821]
820 Ohm [4306R-102-821LF]	820 Ohm [4420P-2-821]	820 Ohm [4610X-101-821LF]	820 Ohm [4816P-T02-821LF]
820 Ohm [4308M-101-821]	820 Ohm [4420P-T02-821]	820 Ohm [4610X-102-821LF]	820 Ohm [CAT16-8200F4LF]
820 Ohm [4308M-102-821]	820 Ohm [4604X-101-821LF]	820 Ohm [4610X-AP1-821LF]	820 Ohm [CAT16-821J4LF]
820 Ohm [4308M-102-821LF]	820 Ohm [4605M-101-821LF]	820 Ohm [4611X-101-821LF]	820 Ohm [CAT25-821JALF]
820 Ohm [4308R-101-821]	820 Ohm [4605X-101-821LF]	820 Ohm [4612X-101-821LF]	820 Ohm [CAY10-821J4LF]

Multisim 14.1 Education Components

820 Ohm [CAY16-821J4LF]	820 Ohm [CR2512-JW-821ELF]	820 pF [C0402C821K8RACTU]	820 pF [C0805C821K1RACTU]
820 Ohm [CAY16-821J8LF]	820 Ohm [CRM1206-FX-8200ELF]	820 pF [C0603C821K1HACTU]	820 pF [C0805C821K2RACTU]
820 Ohm [CR0402-FX-8200GLF]	820 Ohm [PWR163S-25-8200F]	820 pF [C0603C821K1RACTU]	820 pF [C0805C821K4GACTU]
820 Ohm [CR0603-FX-8200ELF]	820 Ohm [PWR163S-25-8200JE]	820 pF [C0603C821K2RACTU]	820 pF [C0805C821K4RACTU]
820 Ohm [CR0603-JW-821ELF]	820 pF [C0402C821K1HACTU]	820 pF [C0603C821K3GACTU]	820 pF [C0805C821K5GACTU]
820 Ohm [CR0603-JW-821GLF]	820 pF [C0402C821K3GACTU]	820 pF [C0603C821K3HACTU]	820 pF [C0805C821K5RACTU]
820 Ohm [CR0805-FX-8200ELF]	820 pF [C0402C821K3HACTU]	820 pF [C0603C821K3RACTU]	820 pF [C1206C821K1GACTU]
820 Ohm [CR0805-FX-8200GLF]	820 pF [C0402C821K3RACTU]	820 pF [C0603C821K4RACTU]	820 pF [C1206C821K2GACTU]
820 Ohm [CR0805-JW-821ELF]	820 pF [C0402C821K4RACTU]	820 pF [C0603C821K5GACTU]	820 pF [C1206C821K5GACTU]
820 Ohm [CR0805-JW-821GLF]	820 pF [C0402C821K5HACTU]	820 pF [C0603C821K5HACTU]	820 pF [C1210C821KBGACTU]
820 Ohm [CR1206-FX-8200ELF]	820 pF [C0402C821K5RACTU]	820 pF [C0603C821K5RACTU]	820 pF [C1812C821K2GACTU]

Multisim 14.1 Education Components

820 pF [C1812C821K5GACT U]	820 uH [SDR0503- 821KL]	820 uH [SRR1206- 821KL]	825 kOhm [CRT1206-BW- 8253ELF]
820 pF [C1812C821KBGAC TU]	820 uH [SDR0604- 821KL]	820 uH [SRR1208- 821KL]	825 Ohm [CAY16- 8250F4LF]
820 pF [C1825C821KBGAC TU]	820 uH [SDR0703- 821KL]	820 uH [SRR1210- 821M]	825 Ohm [CR0402- FX-8250GLF]
820 pF [C2220C821KBGAC TU]	820 uH [SDR0805- 821KL]	820 uH [SRR1210A- 821M]	825 Ohm [CR0603- FX-8250ELF]
820 pF [C2225C821KBGAC TU]	820 uH [SDR0906- 821KL]	820 uH [SRR1240- 821K]	825 Ohm [CR0805- FX-8250ELF]
820 pF [CDR32BP821BKSM]	820 uH [SDR1006- 821KL]	820 uH [SRR1260- 821K]	825 Ohm [CR1206- FX-8250ELF]
820 uF [2SEPC820MD]	820 uH [SDR1307- 821KL]	820 uH [SRR1260A- 821K]	825 Ohm [CRM1206-FX- 8250ELF]
820 uF [2SEPC820MW]	820 uH [SDR1307A-821K]	820 uH [SRR1280- 821K]	825 Ohm [CRT0402-FZ- 8250GLF]
820 uF [2SEPC820MX]	820 uH [SDR6603- 821M]	820 uH [SRR7045- 821M]	825 Ohm [CRT0805-BY- 8250ELF]
820 uF [2SEPC820MY]	820 uH [SRR0745A- 821M]	825 kOhm [CR0402-FX- 8253GLF]	825 Ohm [CRT0805-CX- 8250ELF]
820 uH [SDE1006A- 821K]	820 uH [SRR0805- 821K]	825 kOhm [CR0603-FX- 8253ELF]	825 Ohm [PWR2615W8250FE]
820 uH [SDR0302- 821KL]	820 uH [SRR0906- 821YL]	825 kOhm [CR0805-FX- 8253ELF]	84.5 kOhm [CR0402-FX- 8452GLF]
820 uH [SDR0403- 821KL]	820 uH [SRR0908- 821YL]	825 kOhm [CR1206-FX- 8253ELF]	

Multisim 14.1 Education Components

84.5 kOhm [CR0603-FX- 8452ELF]	845 Ohm [CR0805- FX-8450ELF]	86.6 kOhm [CRT0805-FX- 8662ELF]	866 Ohm [CR0805- FX-8660ELF]
84.5 kOhm [CR0805-FX- 8452ELF]	845 Ohm [CR1206- FX-8450ELF]	86.6 kOhm [CRT1206-BW- 8662ELF]	866 Ohm [CR1206- FX-8660ELF]
84.5 kOhm [CR1206-FX- 8452ELF]	845 Ohm [CRT0805-BY- 8450ELF]	86.6 Ohm [CAT16- 86R6F4LF]	866 Ohm [CRT0402-BY- 8660GLF]
84.5 Ohm [CAY16- 84R5F4LF]	85 mOhm [CRA2512-JZ- R085ELF]	86.6 Ohm [CAY16- 86R6F4LF]	87520-0010BLF
84.5 Ohm [CR0603- FX-84R5ELF]	850 nH [SRP1205- R60Y]	86.6 Ohm [CR0402- FX-86R6GLF]	88.7 kOhm [CR0402-FX- 8872GLF]
84.5 Ohm [CR0805- FX-84R5ELF]	850 Ohm [PWR220T-35- 8500J]	86.6 Ohm [CR0603- FX-86R6ELF]	88.7 kOhm [CR0603-FX- 8872ELF]
84.5 Ohm [CR1206- FX-84R5ELF]	8550-4500PL	86.6 Ohm [CR0805- FX-86R6ELF]	88.7 kOhm [CR0805-FX- 8872ELF]
845 kOhm [CR0402-FX- 8453GLF]	86 kOhm [4116R-1- 863LF]	86.6 Ohm [CR1206- FX-86R6ELF]	88.7 kOhm [CR1206-FX- 8872ELF]
845 kOhm [CR0603-FX- 8453ELF]	86.6 kOhm [CR0201-FW- 8662GLF]	866 kOhm [CR0402-FX- 8663GLF]	88.7 Ohm [CR0603- FX-88R7ELF]
845 kOhm [CR0805-FX- 8453ELF]	86.6 kOhm [CR0402-FX- 8662GLF]	866 kOhm [CR0805-FX- 8663ELF]	88.7 Ohm [CR0805- FX-88R7ELF]
845 kOhm [CR1206-FX- 8453ELF]	86.6 kOhm [CR0603-FX- 8662ELF]	866 kOhm [CR1206-FX- 8663ELF]	88.7 Ohm [CR1206- FX-88R7ELF]
845 Ohm [CR0402- FX-8450GLF]	86.6 kOhm [CR0805-FX- 8662ELF]	866 Ohm [CR0402- FX-8660GLF]	88.7 Ohm [CRM2512-FX- 88R7ELF]
845 Ohm [CR0603- FX-8450ELF]	86.6 kOhm [CR1206-FX- 8662ELF]	866 Ohm [CR0603- FX-8660ELF]	880 nH [SRP4020- R88M]

Multisim 14.1 Education Components

887 kOhm [CR0402-FX- 8873GLF]	9 mOhm [CRE2512- FZ-R009E-3]	9.1 kOhm [4306M- 101-912LF]	9.1 nF [C0603C912K3HACT U]
887 kOhm [CR0603-FX- 8873ELF]	9 mOhm [CRF0805- FX-R009ELF]	9.1 kOhm [CAY16- 912J4LF]	9.1 nF [C0805C912K1GACT U]
887 kOhm [CR0805-FX- 8873ELF]	9 uH [SRP1250- 9R0M]	9.1 kOhm [CR0402- FX-9101GLF]	9.1 nF [C0805C912K1HACT U]
887 kOhm [CR1206-FX- 8873ELF]	9.09 kOhm [CR0402-FX- 9091GLF]	9.1 kOhm [CR0603- JW-912ELF]	9.1 nF [C0805C912K3HACT U]
887 Ohm [CR0402- FX-8870GLF]	9.09 kOhm [CR0603-FX- 9091ELF]	9.1 kOhm [CR0805- FX-9101ELF]	9.1 nF [C0805C912K5GACT U]
887 Ohm [CR0603- FX-8870ELF]	9.09 kOhm [CR0805-FX- 9091ELF]	9.1 kOhm [CR1206- FX-9101ELF]	9.1 nF [C0805C912K5HACT U]
887 Ohm [CR0805- FX-8870ELF]	9.09 kOhm [CR1206-FX- 9091ELF]	9.1 kOhm [CR1206- JW-912ELF]	9.1 nF [C1206C912K1HACT U]
8EQ045	9.09 kOhm [CRT0603-BY- 9091ELF]	9.1 kOhm [CR2512- JW-912ELF]	9.1 nF [C1206C912K3GACT U]
8EWS08S	9.09 kOhm [CRT0603-FY- 9091ELF]	9.1 MOhm [CHV0603-FX- 9104ELF]	9.1 nF [C1206C912K3HACT U]
8EWS10S	9.09 Ohm [PWR6327W9R09F]	9.1 MOhm [CR0805-JW- 915ELF]	9.1 nF [C1206C912K5HACT U]
8EWS12S	9.1 kOhm [4304M- 101-912]	9.1 MOhm [CR1206-JW- 915ELF]	9.1 nF [CDR35BP912BKSM]
8Line_Bussed	9.1 kOhm [4306M- 101-912]		
8Line_Isolated			
8POS_ROTARY			
9 mOhm [CRE2512- FZ-R009E-2]			

Multisim 14.1 Education Components

9.1 Ohm [CR0402-J/-9R1GLF]	9.1 Ohm [FW10A9R10JA]	9.53 kOhm [CRT0805-BW-9531ELF]	90.9 kOhm [CR0402-FX-9092GLF]
9.1 Ohm [CR0603-J/-9R1ELF]	9.1 Ohm [FW20A9R10JA]	9.6 kOhm [4116R-1-962]	90.9 kOhm [CR0603-FX-9092ELF]
9.1 Ohm [CR0805-J/-9R1ELF]	9.1 Ohm [FW70A9R10JA]	9.6 kOhm [4116R-1-962LF]	90.9 kOhm [CR0603-FX-9092GLF]
9.1 Ohm [CR1206-J/-9R1ELF]	9.31 kOhm [CR0402-FX-9311GLF]	9.76 kOhm [CR0402-FX-9761GLF]	90.9 kOhm [CR0805-FX-9092ELF]
9.1 Ohm [CRL0603-FW-9R10ELF]	9.31 kOhm [CR0603-FX-9311ELF]	9.76 kOhm [CR0603-FX-9761ELF]	90.9 kOhm [CR1206-FX-9092ELF]
9.1 Ohm [CRL0805-FW-9R10ELF]	9.31 kOhm [CR0805-FX-9311ELF]	9.76 kOhm [CR0805-FX-9761ELF]	90.9 kOhm [CRM0805-FX-9092ELF]
9.1 Ohm [CRL1206-FW-9R10ELF]	9.31 kOhm [CR1206-FX-9311ELF]	9.76 kOhm [CR1206-FX-9761ELF]	90.9 Ohm [CR0402-FX-90R9GLF]
9.1 Ohm [CRL2010-FW-9R10ELF]	9.31 kOhm [CRT0603-BY-9311ELF]	9.76 kOhm [CRT0805-BV-9761ELF]	90.9 Ohm [CR0603-FX-90R9ELF]
9.1 Ohm [CRL2512-FW-9R10ELF]	9.53 kOhm [CR0402-FX-9531GLF]	9.76 kOhm [CRT0805-BY-9761ELF]	90.9 Ohm [CR0805-FX-90R9ELF]
9.1 Ohm [CRM1206-FX-9R10ELF]	9.53 kOhm [CR0603-FX-9531ELF]	90 mOhm [CRM0805-FW-R090ELF]	90.9 Ohm [CR1206-FX-90R9ELF]
9.1 Ohm [CRM2512-JW-9R1ELF]	9.53 kOhm [CR0805-FX-9531ELF]	90 mOhm [CRM2010-FX-R090ELF]	90.9 Ohm [CRT0805-BY-90R9ELF]
9.1 Ohm [CRT0603-BY-9R10ELF]	9.53 kOhm [CR1206-FX-9531ELF]	90.9 kOhm [CR0201-FW-9092GLF]	900 nH [SRN6028-R90Y]

Multisim 14.1 Education Components

900 nH [SRP1206-R60Y]	91 kOhm [4114R-1-913LF]	91 mF [C0805C919KBGAC TU]	91 Ohm [CR0805-JW-910ELF]
900 nH [SRR1305-R90ZL]	91 kOhm [4116R-1-913]	91 Ohm [4306M-102-910]	91 Ohm [CR1206-FX-91R0ELF]
909 kOhm [CR0402-FX-9093GLF]	91 kOhm [4116R-1-913LF]	91 Ohm [4308M-102-910]	91 Ohm [CR1206-JW-910ELF]
909 kOhm [CR0603-FX-9093ELF]	91 kOhm [CAT16-913J4LF]	91 Ohm [4308M-102-910LF]	91 Ohm [CR2512-JW-910ELF]
909 kOhm [CR0805-FX-9093ELF]	91 kOhm [CAY16-913J4LF]	91 Ohm [4608X-102-910LF]	91 Ohm [CRM2512-JW-910ELF]
909 kOhm [CR1206-FX-9093ELF]	91 kOhm [CR0201-FW-9102GLF]	91 Ohm [4820P-1-910]	91 pF [C0805C910K2GACT U]
909 Ohm [CR0402-FX-9090GLF]	91 kOhm [CR0402-FX-9102GLF]	91 Ohm [4820P-T02-910]	91 pF [C0805C910KBGAC TU]
909 Ohm [CR0603-FX-9090ELF]	91 kOhm [CR0402-JW-913GLF]	91 Ohm [CAT10-910J4LF]	91 pF [C1206C910K1GACT U]
909 Ohm [CR0805-FX-9090ELF]	91 kOhm [CR0603-FX-9102ELF]	91 Ohm [CAY16-910J4LF]	91 pF [C1206C910KBGAC TU]
909 Ohm [CR1206-FX-9090ELF]	91 kOhm [CR0603-JW-913ELF]	91 Ohm [CAY16-91R0F4LF]	91 pF [C1210C910KBGAC TU]
909 Ohm [CR2512-FX-9090ELF]	91 kOhm [CR0805-FX-9102ELF]	91 Ohm [CR0402-FX-91R0GLF]	91 pF [C1812C910KBGAC TU]
909 Ohm [CRT0402-FZ-9090GLF]	91 kOhm [CR1206-FX-9102ELF]	91 Ohm [CR0603-FX-91R0ELF]	91 pF [C1825C910KBGAC TU]
90CLQ100	91 kOhm [CR1206-JW-913ELF]	91 Ohm [CR0603-JW-910ELF]	
91 kOhm [4114R-1-913]	91 kOhm [CRT0603-BZ-9102ELF]	91 Ohm [CR0805-FX-91R0ELF]	

Multisim 14.1 Education Components

91 pF [C2220C910KBGAC TU]	910 kOhm [CR1206-JW- 914ELF]	910 mOhm [CRL2512-JW- R910ELF]	910 Ohm [CR0402- FX-9100GLF]
91 pF [C2225C910KBGAC TU]	910 kOhm [CRT0805-BY- 9103ELF]	910 mOhm [CRM0805-FX- R910ELF]	910 Ohm [CR0402- JW-911GLF]
910 kOhm [CAY16- 914J4LF]	910 mOhm [CRL0603-FW- R910ELF]	910 mOhm [CRM1206-FX- R910ELF]	910 Ohm [CR0603- FX-9100ELF]
910 kOhm [CHV0603-FX- 9103ELF]	910 mOhm [CRL0603-JW- R910ELF]	910 mOhm [CRM2010-FX- R910ELF]	910 Ohm [CR0805- FX-9100ELF]
910 kOhm [CR0402-FX- 9103GLF]	910 mOhm [CRL0805-FW- R910ELF]	910 mOhm [CRM2512-FX- R910ELF]	910 Ohm [CR0805- JW-911ELF]
910 kOhm [CR0402-JW- 914GLF]	910 mOhm [CRL0805-JW- R910ELF]	910 mOhm [CRM2512-JX- R910ELF]	910 Ohm [CR1206- JW-911ELF]
910 kOhm [CR0603-FX- 9103ELF]	910 mOhm [CRL1206-FW- R910ELF]	910 Ohm [4116R-1- 911]	910 Ohm [CR2010- JW-911ELF]
910 kOhm [CR0603-JW- 914ELF]	910 mOhm [CRL1206-JW- R910ELF]	910 Ohm [4308H- 101-911]	910 Ohm [CR2512- JW-911ELF]
910 kOhm [CR0805-FX- 9103ELF]	910 mOhm [CRL2010-FW- R910ELF]	910 Ohm [4308R- 101-911]	910 Ohm [CRT1206-AV- 9100ELF]
910 kOhm [CR0805-JW- 914ELF]	910 mOhm [CRL2010-JW- R910ELF]	910 Ohm [4310H- 101-911]	910 Ohm [CRT1206-BY- 9100ELF]
910 kOhm [CR1206-FX- 9103ELF]	910 mOhm [CRL2512-FW- R910ELF]	910 Ohm [CAY10- 911J4LF]	910 pF [C0402C911K1HACT U]
		910 Ohm [CAY16- 911J4LF]	910 pF [C0402C911K3HACT U]

Multisim 14.1 Education Components

910 pF [C0402C911K5HACT U]	93.1 kOhm [CR0402-FX- 9312GLF]	931 kOhm [CR1206-FX- 9313ELF]	95 Ohm [4816P-2- 950]
910 pF [C0603C911K1HACT U]	93.1 kOhm [CR0603-FX- 9312ELF]	931 Ohm [CR0402- FX-9310GLF]	95 Ohm [4816P-2- 950LF]
910 pF [C0603C911K3HACT U]	93.1 kOhm [CR0805-FX- 9312ELF]	931 Ohm [CR0603- FX-9310ELF]	95 Ohm [4818P-1- 950]
910 pF [C0603C911K5GACT U]	93.1 kOhm [CR1206-FX- 9312ELF]	931 Ohm [CR0805- FX-9310ELF]	95.3 kOhm [CR0201-FW- 9532GLF]
910 pF [C0603C911K5HACT U]	93.1 Ohm [CR0402- FX-93R1GLF]	931 Ohm [CR1206- FX-9310ELF]	95.3 kOhm [CR0402-FX- 9532GLF]
910 pF [C0805C911K5GACT U]	93.1 Ohm [CR0603- FX-93R1ELF]	931 Ohm [CRM2512-FX- 9310ELF]	95.3 kOhm [CR0603-FX- 9532ELF]
910 pF [C0805C911K5GACT U]	93.1 Ohm [CR0805- FX-93R1ELF]	931 Ohm [CRT0603-BY- 9310ELF]	95.3 kOhm [CR0805-FX- 9532ELF]
910 pF [C1210C911KBGAC TU]	93.1 Ohm [CR1206- FX-93R1ELF]	95 mOhm [CRA2512-JZ- R095ELF]	95.3 kOhm [CR0805-FX- 9532ELF]
910 pF [C1812C911KBGAC TU]	93.1 Ohm [CR2010- FX-93R1ELF]	95 Ohm [4114R-2- 950LF]	95.3 kOhm [CR1206-FX- 9532ELF]
910 pF [C1825C911KBGAC TU]	931 kOhm [CR0402-FX- 9313GLF]	95 Ohm [4306R- 101-950]	95.3 kOhm [CRT0603-BY- 9532ELF]
910 pF [C1825C911KBGAC TU]	931 kOhm [CR0603-FX- 9313ELF]	95 Ohm [4308H- 101-950]	95.3 kOhm [CRT0805-BW- 9532ELF]
910 pF [C2220C911KBGAC TU]	931 kOhm [CR0805-FX- 9313ELF]	95 Ohm [4308H- 101-950LF]	95.3 Ohm [CR0402- FX-95R3GLF]
910 pF [C2225C911KBGAC TU]		95 Ohm [4310H- 102-950]	95.3 Ohm [CR0603- FX-95R3ELF]
		95 Ohm [4816P-1- 950]	95.3 Ohm [CR0805- FX-95R3ELF]

Multisim 14.1 Education Components

95.3 Ohm [CR1206-FX-95R3ELF]	97.6 kOhm [CR0603-FX-9762ELF]	976 kOhm [CR1206-FX-9763ELF]	ACA3216M3-600
95.3 Ohm [CRT0402-FZ-95R3GLF]	97.6 kOhm [CR0805-FX-9762ELF]	976 Ohm [CR0402-FX-9760GLF]	ACA3216M4-060
953 kOhm [CR0402-FX-9533GLF]	97.6 kOhm [CR1206-FX-9762ELF]	976 Ohm [CR0603-FX-9760ELF]	ACA3216M4-120
953 kOhm [CR0603-FX-9533ELF]	97.6 kOhm [CRT0603-BY-9762ELF]	976 Ohm [CR0805-FX-9760ELF]	ACA3216M4-300
953 kOhm [CR0805-FX-9533ELF]	97.6 kOhm [CRT0805-BY-9762ELF]	976 Ohm [CR0805-FX-9760GLF]	ACA3216M4-600
953 kOhm [CR1206-FX-9533ELF]	97.6 Ohm [CR0402-FX-97R6GLF]	976 Ohm [CR1206-FX-9760ELF]	ACB1608H-015
953 Ohm [CR0402-FX-9530GLF]	97.6 Ohm [CR0603-FX-97R6ELF]	9Line_Bussed	ACB1608H-030
953 Ohm [CR0603-FX-9530ELF]	97.6 Ohm [CR0805-FX-97R6ELF]	9Line_Isolated	ACB1608H-060
953 Ohm [CR0805-FX-9530ELF]	976 kOhm [CR0402-FX-9763GLF]	A+jB_BLOCK	ACB1608H-120
953 Ohm [CR1206-FX-9530ELF]	976 kOhm [CR0603-FX-9763ELF]	ABC_TO_DQ	ACB1608H-300
97.6 kOhm [CR0402-FX-9762GLF]	976 kOhm [CR0805-FX-9763ELF]	ABM_CURRENT	ACB1608L-015
		ABM_VOLTAGE	ACB1608L-030
		AC_CURRENT	ACB1608L-060
		AC_POWER	ACB1608L-120
		AC_VOLTAGE	ACB1608L-300
		ACA3216H4-060	ACB1608M-040
		ACA3216H4-120	ACB1608M-080
		ACA3216H4-300	ACB1608M-120
			ACB1608M-300
			ACB1608M-600
			ACB2012H-015
			ACB2012H-030
			ACB2012H-060
			ACB2012H-120
			ACB2012H-300

Multisim 14.1 Education Components

ACB2012L-015	ACPL-021L-060E	ACPL-312U-000E	ACPL-K30T-000E
ACB2012L-030	ACPL-024L-000E	ACPL-312U-300E	ACPL-K30T-060E
ACB2012L-060	ACPL-024L-060E	ACPL-32JT-000E	ACPL-K342-000E
ACB2012L-120	ACPL-054L-000E	ACPL-331J-000E	ACPL-K342-060E
ACB2012L-300	ACPL-054L-060E	ACPL-332J-000E	ACPL-K34T-000E
ACB2012L-600	ACPL-061L-000E	ACPL-336J-000E	ACPL-K34T-060E
ACB2012M-040	ACPL-061L-060E	ACPL-337J-000E	ACPL-K43T-000E
ACB2012M-080	ACPL-064L-000E	ACPL-339J-000E	ACPL-K43T-060E
ACB2012M-120	ACPL-064L-060E	ACPL-34JT-000E	ACPL-K44T-000E
ACB2012M-300	ACPL-077L-000E	ACPL-782T-000E	ACPL-K44T-060E
ACB2012M-600	ACPL-077L-060E	ACPL-782T-300E	ACPL-K54L-000E
ACC2012L-250	ACPL-214-500E	ACPL-796J-000E	ACPL-K54L-060E
ACC3216L-500	ACPL-214-50AE	ACPL-796J-060E	ACPL-K64L-000E
ACC4516L-700	ACPL-214-560E	ACPL-798J-000E	ACPL-K64L-060E
ACML-7400-000E	ACPL-214-56AE	ACPL-C61L-000E	ACPL-M21L-000E
ACML-7410-000E	ACPL-217-500E	ACPL-C61L-060E	ACPL-M21L-060E
ACML-7420-000E	ACPL-217-50AE	ACPL-C790-000E	ACPL-M43T-000E
ACNT-H313-000E	ACPL-217-50BE	ACPL-C797-000E	ACPL-M43T-060E
ACNW261L-000E	ACPL-217-50CE	ACPL-C799-000E	ACPL-M46T-000E
ACNW261L-300E	ACPL-217-50DE	ACPL-C79A-000E	ACPL-M46T-060E
ACNW3410-000E	ACPL-217-560E	ACPL-C79B-000E	ACPL-M483-000E
ACNW3410-300E	ACPL-217-56AE	ACPL-C87AT-000E	ACPL-M483-060E
ACNW3430-000E	ACPL-217-56BE	ACPL-C87BT-000E	ACPL-M484-000E
ACNW3430-300E	ACPL-217-56CE	ACPL-H342-000E	ACPL-M484-060E
ACPL-021L-000E	ACPL-217-56DE	ACPL-H342-060E	ACPL-M49T-000E

Multisim 14.1 Education Components

ACPL-M49T-060E	ACPL-P483-000E	ACPL-W61L-060E	AD509SH
ACPL-M50L-000E	ACPL-P483-060E	ACSL-6400-00TE	AD515AJH
ACPL-M50L-060E	ACPL-P484-000E	ACSL-6400-06TE	AD515AKH
ACPL-M61L-000E	ACPL-P484-060E	ACSL-7210-00RE	AD515ALH
ACPL-M61L-060E	ACPL-W340-000E	ACSL-7210-06RE	AD517JH
ACPL-M61T-000E	ACPL-W340-060E	ACTEL-FLASHPRO- HDR	AD517KH
ACPL-M61T-060E	ACPL-W341-000E		AD517LH
ACPL-M71T-000E	ACPL-W341-060E	AD1580ART	AD517SH
ACPL-M71T-060E	ACPL-W343-000E	AD1580ARTZ	AD536AJD
ACPL-M72T-000E	ACPL-W343-060E	AD1580BKSZ	AD536AJH
ACPL-M72T-060E	ACPL-W345-000E	AD1580BRT	AD536AJQ
ACPL-P340-000E	ACPL-W345-060E	AD1580BRTZ	AD536ASE/883B
ACPL-P340-060E	ACPL-W346-000E	AD22050N	AD542JH
ACPL-P341-000E	ACPL-W346-060E	AD22050R	AD542KH
ACPL-P341-060E	ACPL-W347-000E	AD22057N	AD542LH
ACPL-P343-000E	ACPL-W347-060E	AD22057R	AD542SH
ACPL-P343-060E	ACPL-W349-000E	AD380JH	AD544JH
ACPL-P345-000E	ACPL-W349-060E	AD380KH	AD544KH
ACPL-P345-060E	ACPL-W483-000E	AD380LH	AD544LH
ACPL-P346-000E	ACPL-W483-060E	AD380SH	AD544SH
ACPL-P346-060E	ACPL-W484-000E	AD507JH	AD545AJH
ACPL-P347-000E	ACPL-W484-060E	AD507KH	AD545AKH
ACPL-P347-060E	ACPL-W50L-000E	AD507SH	AD545ALH
ACPL-P349-000E	ACPL-W50L-060E	AD509JH	AD545AMH
ACPL-P349-060E	ACPL-W61L-000E	AD509KH	AD546JN

Multisim 14.1 Education Components

AD546KN	AD549LHZ	AD587JR	AD604AR
AD547JH	AD549SH	AD587JRZ	AD604ARS
AD547KH	AD549SH/883B	AD587KN	AD605AN
AD547LH	AD5530_SO16	AD587KR	AD605AR
AD547SH	AD5531_SO16	AD587KRZ	AD620AN
AD548AH	AD5539JN	AD587UQ	AD620AR
AD548AQ	AD5539JQ	AD588AD	AD620BN
AD548AR	AD5539SQ	AD588AQ	AD620BR
AD548BH	AD5539SQ/883B	AD588ARWZ	AD620SQ
AD548BQ	AD581JH	AD588BD	AD623AN
AD548BR	AD581KH	AD588BQ	AD623AR
AD548CH	AD581LH	AD588JQ	AD623ARM
AD548CQ	AD581SH	AD588KQ	AD623BN
AD548JN	AD581TH	AD588SD	AD623BR
AD548JR	AD581UH	AD588TD	AD624AD
AD548KN	AD584JH	AD588TQ/883B	AD624BD
AD548SH	AD584JN	AD600AQ	AD624CD
AD548SQ	AD584KH	AD600AR	AD624SD
AD548TH	AD584KN	AD600JN	AD626AN
AD548TQ	AD584LH	AD602AQ	AD626AR
AD549JH	AD584SH	AD602AR	AD626BN
AD549JHZ	AD584TH	AD602JN	AD627AN
AD549KH	AD587JN	AD603AQ	AD627AR
AD549KHZ	AD587JNZ	AD603AR	AD627BN
AD549LH	AD587JQ	AD604AN	AD627BR

Multisim 14.1 Education Components

AD628ARMZ	AD637ARZ	AD645JN	AD705JN
AD628ARZ	AD637BR	AD645KN	AD705JR
AD629AN	AD637BRZ	AD645SH	AD705KN
AD629AR	AD637JD	AD647JH	AD705TQ
AD629BN	AD637JDZ	AD647KH	AD706AQ
AD629BR	AD637JQ	AD647LH	AD706AR
AD630AD	AD637JRZ	AD647SE	AD706BQ
AD630AR	AD637JRZ-R7	AD647SEB	AD706JN
AD630BD	AD637JRZ-RL	AD647SH	AD706JR
AD630JN	AD637KDZ	AD680AN	AD706KN
AD630KN	AD637KQ	AD680AR	AD706TQ
AD630SD	AD637KRZ	AD680JR	AD707AH
AD630SE/883B	AD637SD	AD680JTZ	AD707AQ
AD633AN	AD637SD/883B	AD704AN	AD707AR
AD633ANZ	AD637SQ/883B	AD704AQ	AD707JN
AD633AR	AD642JH	AD704AR	AD707KN
AD633ARZ	AD642KH	AD704BQ	AD707KR
AD633JN	AD642LH	AD704JN	AD707TH
AD633JR	AD642SH	AD704JR	AD707TQ
AD636JD	AD644JH	AD704JR-16	AD708AH
AD636JH	AD644KH	AD704KN	AD708AQ
AD636KD	AD644LH	AD704TQ	AD708BH
AD636KH	AD644SH	AD704TQ/883B	AD708BQ
AD637AQ	AD645AH	AD705AQ	AD708JN
AD637AR	AD645BH	AD705BQ	AD708SH

Multisim 14.1 Education Components

AD708SH/883B	AD712KR	AD736JNZ	AD744AQ
AD708SQ	AD712SH	AD737AN	AD744BH
AD711AH	AD712SQ	AD737AR	AD744BQ
AD711AQ	AD712SQ/883B	AD737BQ	AD744CH
AD711BH	AD712TH	AD741CH	AD744CQ
AD711BQ	AD712TQ	AD741CN	AD744JN
AD711CH	AD712TRZ-EP	AD741H	AD744JR
AD711CQ	AD713AQ	AD741JH	AD744KN
AD711JN	AD713BQ	AD741JN	AD744KR
AD711JR	AD713JN	AD741KH	AD744SH
AD711KN	AD713JR	AD741KN	AD744SQ
AD711KR	AD713JR-16	AD741LH	AD744TH
AD711SH	AD713KN	AD741LN	AD744TH/883B
AD711SQ	AD713SQ	AD741SH	AD744TQ
AD711TH	AD713SQ/883B	AD743AN	AD745AN
AD711TQ	AD713TQ	AD743AQ	AD745AQ
AD712AH	AD713TQ/883B	AD743AR	AD745AR
AD712AQ	AD734AN	AD743BQ	AD745BQ
AD712BH	AD734AQ	AD743JN	AD745JN
AD712BQ	AD734BN	AD743JR	AD745JR
AD712CH	AD734BQ	AD743KN	AD745KN
AD712CQ	AD734SQ	AD743KR	AD745SQ
AD712JN	AD734SQ/883B	AD743SQ	AD745SQ/883B
AD712JR	AD736AQ	AD743SQ/883B	AD746AQ
AD712KN	AD736AR	AD744AH	AD746BQ

Multisim 14.1 Education Components

AD746JN	AD8001AR	AD8011AR	AD8027ARTZ
AD746JR	AD8001ART	AD8012AR	AD8027ARTZ-R2
AD746SQ	AD8002AN	AD8012ARM	AD8027ARTZ-REEL
AD780AN	AD8002AR	AD8012ARMZ	AD8027ARTZ-REEL7
AD780AR	AD8002ARM	AD8014AR	AD8027ARZ
AD780BN	AD8003ACPZ	AD8014ART	AD8027ARZ-REEL
AD780BR	AD8003ACPZ-R2	AD8016ARB	AD8027ARZ-REEL7
AD795BH	AD8004AN	AD8016ARE	AD8028ARMZ
AD795JN	AD8004AR	AD8016AREZ	AD8028ARZ
AD795JR	AD8004AR-14	AD8016ARP	AD8029AKS
AD795JRZ	AD8004SQ	AD8017AR	AD8029AKSZ-R2
AD795KN	AD8005AN	AD8018AR	AD8029AR
AD796AN	AD8005AR	AD8018ARU	AD8029ARZ
AD796AR	AD8005ART	AD8021AR	AD8030AR
AD796BN	AD8007AKS	AD8021ARM	AD8030ARJ
AD796SQ/883B	AD8007AR	AD8021ARMZ	AD8030ARJZ-R2
AD797AN	AD8008AR	AD8021ARZ	AD8030ARZ
AD797AR	AD8008ARM	AD8022AR	AD8031AN
AD797BN	AD8009AR	AD8022ARM	AD8031ANZ
AD797SQ	AD8009ARZ	AD8022ARMZ	AD8031AR
AD8000YCPZ	AD8009JRT	AD8022ARZ	AD8031ART
AD8000YCPZ-REEL	AD8010AN	AD8023AR	AD8031ARTZ
AD8000YRDZ	AD8010AR	AD8024AR	AD8031ARZ
AD8001AN	AD8010AR-16	AD8027AR	AD8031BN
AD8001AQ	AD8011AN	AD8027ART	AD8031BNZ

Multisim 14.1 Education Components

AD8031BR	AD8039ART	AD8054AR	AD8066AR
AD8031BRZ	AD8039ARTZ-R2	AD8054ARU	AD8066ARM
AD8032AN	AD8039ARZ	AD8055AN	AD8066ARMZ
AD8032ANZ	AD8040AR	AD8055AR	AD8066ARZ
AD8032AR	AD8040ARU	AD8055ART	AD8067ART
AD8032ARM	AD8040ARUZ	AD8055ARZ	AD8067ARTZ-R2
AD8032ARMZ	AD8040ARZ	AD8056AN	AD8072ARM
AD8032ARZ	AD8041AN	AD8056AR	AD8072JN
AD8032BN	AD8041AR	AD8056ARM	AD8072JR
AD8032BNZ	AD8042AN	AD8057AR	AD8079AR
AD8032BR	AD8042AR	AD8057ART	AD8079BR
AD8032BRZ	AD8044AN	AD8057ARTZ-R2	AD8091AR
AD8033AKS	AD8044AR	AD8057ARZ	AD8091ART
AD8033AR	AD8045ACP	AD8058AR	AD8092AR
AD8034AR	AD8045ACPZ-R2	AD8058ARM	AD8092ARM
AD8034ART	AD8045ARD	AD8061AR	AD8099ACP
AD8034ARTZ-R2	AD8045ARDZ	AD8061ART	AD8099ACPZ-R2
AD8034ARZ	AD8047AN	AD8062AR	AD8099ARD
AD8036AN	AD8047AR	AD8062ARM	AD8099ARDZ
AD8036AR	AD8048AN	AD8062ARMZ	AD810AN
AD8038AKS	AD8048AR	AD8062ARZ	AD810AR
AD8038AKSZ-R2	AD8051AR	AD8065AR	AD810SN
AD8038AR	AD8051ART	AD8065ART	AD810SR
AD8038ARZ	AD8052AR	AD8065ARTZ	AD811AN
AD8039AR	AD8052ARM	AD8065ARZ	AD811AR-16

Multisim 14.1 Education Components

AD811AR-20	AD8137YCPZ	AD8205WHRZ	AD8210YRZ
AD811JR	AD8137YR	AD8205WHRZ-RL	AD8211YRJZ-R2
AD811SE/883B	AD8137YRZ	AD8205WYRZ	AD8214ARMZ
AD811SQ/883B	AD8138AR	AD8205WYRZ-R7	AD8216WYRZ
AD8129ARMZ	AD8138ARM	AD8205WYRZ-RL	AD8216WYRZ-R7
AD8129ARMZ-REEL	AD8138ARMZ	AD8205YRZ	AD8216WYRZ-RL
AD8129ARMZ-REEL7	AD8138ARZ	AD8205YRZ-R7	AD8216YRZ
AD8129ARZ	AD8139ACP	AD8205YRZ-RL	AD8216YRZ-R7
AD8129ARZ-REEL	AD8139ACPZ	AD8206WYRZ	AD8216YRZ-RL
AD8129ARZ-REEL7	AD8139ACPZ-R2	AD8206WYRZ-R7	AD8217BRMZ
AD812AN	AD8139ARD	AD8206WYRZ-RL	AD8217BRMZ-R7
AD812AR	AD8139ARDZ	AD8206YRZ	AD8217BRMZ-RL
AD8130AR	AD813AN	AD8206YRZ-REEL	AD8218BCPZ-RL
AD8130ARM	AD813AR	AD8206YRZ-REEL7	AD8218BRMZ
AD8131AR	AD813AR-14	AD8207WBRZ	AD8218BRMZ-R7
AD8131ARM	AD8145YCPZ-R2	AD8207WBRZ-R7	AD8219BRMZ
AD8131ARMZ	AD8146ACPZ-R2	AD8207WBRZ-RL	AD8219BRMZ-RL
AD8131ARZ	AD8147ACPZ-R2	AD8208WBRMZ	AD8220ARMZ
AD8132AR	AD8148ACPZ-R2	AD8208WBRZ	AD8220ARMZ-R7
AD8132ARM	AD815ARB-24	AD8209WBRMZ	AD8220ARMZ-RL
AD8132ARMZ	AD817AN	AD820AN	AD8220BRMZ
AD8132ARZ	AD817AR	AD820AR	AD8220BRMZ-R7
AD8133ACP-R2	AD8184AN	AD820BN	AD8220BRMZ-RL
AD8137YCP	AD818AN	AD820BR	AD8220WARMZ
	AD818AR	AD8210WYRZ	AD8220WARMZ-R7

Multisim 14.1 Education Components

AD8220WARMZ-RL	AD8226ARMZ	AD823AN	AD8274ARZ
AD8221AR	AD8226ARZ	AD823ANZ	AD8274ARZ-R7
AD8221ARM	AD8226BRMZ	AD823AR	AD8274ARZ-RL
AD8221ARMZ	AD8226BRZ	AD8244ARMZ	AD8275ARMZ
AD8221ARZ	AD8227ARMZ	AD8244BRMZ	AD8275BRMZ
AD8221BR	AD8227ARZ	AD824AN	AD8276ARMZ
AD8221BRZ	AD8227BRMZ	AD824AR-14	AD8276ARZ
AD8221TRMZ-EP	AD8227BRZ	AD824AR-16	AD8276BRMZ
AD8222ACPZ-R7	AD8228ARMZ	AD824BN	AD8276BRZ
AD8222BCPZ-R7	AD8228ARZ	AD8250ARMZ	AD8277ARZ
AD8222HACPZ-R7	AD8228BRMZ	AD8251ARMZ	AD8277BRZ
AD8222HBCPZ-R7	AD8228BRZ	AD8253ARMZ	AD8278ARMZ
AD8224ACPZ-R7	AD8229HDZ	AD8253ARMZ-R7	AD8278ARZ
AD8224ACPZ-RL	AD822AN	AD8253ARMZ-RL	AD8278BRMZ
AD8224ACPZ-WP	AD822AR	AD825AR	AD8278BRZ
AD8224BCPZ-R7	AD822ARM	AD825AR-16	AD8279ARZ
AD8224BCPZ-RL	AD822BN	AD826AN	AD8279BRZ
AD8224BCPZ-WP	AD822BR	AD826AR	AD827AQ
AD8224HACPZ-R7	AD822SQ	AD8270ACPZ-R7	AD827JN
AD8224HACPZ-RL	AD8232ACPZ-R7	AD8273ARZ	AD827JR-16
AD8224HACPZ-WP	AD8235ACBZ-P7	AD8273ARZ-R7	AD827SE/883B
AD8224HBCPZ-R7	AD8236ARMZ	AD8273ARZ-RL	AD827SQ
AD8224HBCPZ-RL	AD8237ARMZ	AD8274ARMZ	AD827SQ/883B
AD8224HBCPZ-WP	AD8237ARMZ-R7	AD8274ARMZ-R7	AD828AN
AD8225AR	AD8237ARMZ-RL	AD8274ARMZ-RL	AD828AR

Multisim 14.1 Education Components

AD829AQ	AD8332ARUZ	AD8345SQ/883B	AD8418WBRZ
AD829JN	AD8332ARUZ-R7	AD835ANZ	AD841JH
AD829JR	AD8332ARUZ-RL	AD835AR	AD841JN
AD829SE/883B	AD8333ACPZ-REEL	AD835ARZ	AD841JQ
AD829SQ	AD8333ACPZ-REEL7	AD8397ARDZ	AD841KH
AD829SQ/883B	AD8333ACPZ-WP	AD8397ARZ	AD841KN
AD8304ARU	AD8334ACPZ	AD840JN	AD841KQ
AD830AN	AD8334ACPZ-REEL	AD840JQ	AD841SE
AD830JR	AD8334ACPZ-REEL7	AD840KN	AD841SH
AD8310ARM	AD8335ACPZ	AD840KQ	AD841SQ
AD8330ACPZ-R2	AD8335ACPZ-REEL	AD840SE-883B	AD8420ARMZ
AD8330ACPZ-R7	AD8335ACPZ-REEL7	AD840SQ	AD8420ARMZ-R7
AD8330ACPZ-RL	AD8336ACPZ-R7	AD840SQ-883B	AD8420ARMZ-RL
AD8330ARQZ	AD8336ACPZ-RL	AD8417BRMZ	AD8421ARMZ
AD8330ARQZ-R7	AD8336ACPZ-WP	AD8417WBRMZ	AD8421ARMZ-R7
AD8330ARQZ-RL	AD8337BCPZ-R2	AD8417WBRZ	AD8421ARMZ-RL
AD8331ARQZ	AD8337BCPZ-REEL	AD8417WHRMZ	AD8421ARZ
AD8331ARQZ-R7	AD8337BCPZ-REEL7	AD8417WHRZ	AD8421ARZ-R7
AD8331ARQZ-RL	AD8337BCPZ-WP	AD8418ABRMZ	AD8421ARZ-RL
AD8332ACPZ-R2	AD8338ACPZ-R7	AD8418AWBRMZ	AD8421BRMZ
AD8332ACPZ-R7	AD8338ACPZ-RL	AD8418AWBRZ	AD8421BRMZ-R7
AD8332ACPZ-RL	AD834AQ	AD8418AWHRMZ	AD8421BRMZ-RL
AD8332ARU	AD834ARZ	AD8418AWHRZ	AD8421BRZ
AD8332ARU-REEL	AD834JNZ	AD8418BRMZ	AD8421BRZ-R7
AD8332ARU-REEL7	AD834JRZ	AD8418WBRMZ	AD8421BRZ-RL

Multisim 14.1 Education Components

AD8421TRMZ-EP	AD842JH	AD843JN	AD846AQ
AD8421TRMZ-EP-R7	AD842JN	AD843JR	AD846BQ
AD8422ARMZ	AD842JQ	AD843JR-16	AD846SQ
AD8422ARMZ-R7	AD842JR	AD843KN	AD8475ACPZ-R7
AD8422ARMZ-RL	AD842KH	AD843SE	AD8475ACPZ-RL
AD8422ARZ	AD842KN	AD843SE/883B	AD8475ACPZ-WP
AD8422ARZ-R7	AD842KQ	AD843SH	AD8475ARMZ
AD8422ARZ-RL	AD842SE	AD843SQ	AD8475ARMZ-R7
AD8422BRMZ	AD842SH	AD843SQ/883B	AD8475ARMZ-RL
AD8422BRMZ-R7	AD842SQ	AD844AN	AD8475BRMZ
AD8422BRMZ-RL	AD8436ACPZ-R7	AD844AQ	AD8475BRMZ-R7
AD8422BRZ	AD8436ACPZ-RL	AD844BQ	AD8475BRMZ-RL
AD8422BRZ-R7	AD8436ACPZ-WP	AD844JRZ-16	AD8476ACPZ-R7
AD8422BRZ-RL	AD8436ARQZ	AD844SQ	AD8476ACPZ-RL
AD8426ACPZ-R7	AD8436ARQZ-R7	AD8450ASTZ	AD8476ACPZ-WP
AD8426ACPZ-WP	AD8436ARQZ-RL	AD8451ASTZ	AD8476ARMZ
AD8426BCPZ-R7	AD8436BRQZ	AD845AQ	AD8476ARMZ-R7
AD8426BCPZ-WP	AD8436BRQZ-R7	AD845BQ	AD8476ARMZ-RL
AD8428ARZ	AD8436BRQZ-RL	AD845JN	AD8476BCPZ-R7
AD8428BRZ	AD8436JCPZ-R7	AD845JR	AD8476BCPZ-RL
AD8429ARZ	AD8436JCPZ-RL	AD845JR-16	AD8476BCPZ-WP
AD8429ARZ-R7	AD8436JCPZ-WP	AD845KN	AD8476BRMZ
AD8429BRZ	AD843AQ	AD845SQ	AD8476BRMZ-R7
AD8429BRZ-R7	AD843BH	AD845SQ/883B	AD8476BRMZ-RL
	AD843BQ	AD846AN	AD8479ARZ

Multisim 14.1 Education Components

AD8479ARZ-RL	AD8496CRMZ-R7	AD8513AR	AD8534ARZ
AD8479BRZ	AD8497ARMZ	AD8513ARU	AD8538ARZ
AD8479BRZ-RL	AD8497ARMZ-R7	AD8515AKS	AD8538AUJZ
AD847AQ	AD8497CRMZ	AD8515ART	AD8538AUJZ-R2
AD847AR	AD8497CRMZ-R7	AD8517ART	AD8539ARMZ
AD847JN	AD849AQ	AD8519AKS	AD8539ARZ
AD847JR	AD849JN	AD8519AR	AD8541AKS
AD847SQ	AD849JR	AD8519ART	AD8541AR
AD847SQ/883B	AD849SQ	AD8527AR	AD8541ART
AD848AQ	AD849SQ/883B	AD8529AR	AD8541ARZ
AD848JN	AD8500AKSZ	AD8529ARM	AD8542AR
AD848JR	AD8500AKSZ-R2	AD8531AKS	AD8542ARM
AD848SQ	AD8502ARJZ	AD8531AKSZ-R2	AD8542ARU
AD848SQ/883B	AD8504ARUZ	AD8531AR	AD8544AR
AD8494ARMZ	AD8505ACBZ-R7	AD8531ARTZ-REEL	AD8544ARU
AD8494ARMZ-R7	AD8505ARJZ-RL	AD8531ARZ	AD8546ARMZ
AD8494CRMZ	AD8506ARMZ	AD8532AR	AD8548ARZ
AD8494CRMZ-R7	AD8508ACBZ-REEL	AD8532ARM	AD8548ARZ-R7
AD8495ARMZ	AD8508ARUZ	AD8532ARMZ-R2	AD8548ARZ-RL
AD8495ARMZ-R7	AD8510AR	AD8532ARU	AD8551AR
AD8495CRMZ	AD8510ARM	AD8532ARUZ	AD8551ARM
AD8495CRMZ-R7	AD8510BR	AD8532ARZ	AD8552AR
AD8496ARMZ	AD8512AR	AD8534AR	AD8552ARU
AD8496ARMZ-R7	AD8512ARM	AD8534ARU	AD8554AR
AD8496CRMZ	AD8512BR	AD8534ARUZ	AD8554ARU

Multisim 14.1 Education Components

AD8561AN	AD8604ARQZ	AD8611AR	AD8625ARUZ
AD8561AR	AD8604ARUZ	AD8611ARM	AD8625ARZ
AD8561ARU	AD8604DRU	AD8612ARU	AD8626ARMZ
AD8564AN	AD8604DRZ	AD8613AKSZ	AD8626ARZ
AD8564AR	AD8605ACB	AD8613AUJZ	AD8627AKS
AD8565AKS	AD8605ACBZ-REEL7	AD8614ART	AD8627AKSZ
AD8565AKSZ	AD8605ART	AD8615AUJZ	AD8627AR
AD8571AR	AD8605ARTZ-R2	AD8616AR	AD8627ARZ
AD8571ARM	AD8606ACBZ-REEL	AD8616ARM	AD8628AR
AD8572AR	AD8606AR	AD8617ACPZ-R2	AD8628ART
AD8572ARU	AD8606ARM-REEL	AD8617ARMZ	AD8628AUJ
AD8574AR	AD8606ARMZ-REEL	AD8617ARZ	AD8629ARMZ
AD8574ARU	AD8606ARZ	AD8617WARMZ-REEL	AD8629ARZ
AD8591ART	AD8607AR	AD8617WARZ-RL	AD8629WARZ-RL
AD8592ARM	AD8607ARM-REEL	AD8618AR	AD8630ARUZ
AD8594AR	AD8608AR	AD8618ARU	AD8630ARZ
AD8594ARU	AD8608ARU	AD8619ARUZ	AD8630WARZ-RL
AD8597ACPZ-R2	AD8608ARUZ	AD8619ARZ	AD8631ART
AD8597ARZ	AD8608ARZ	AD8620AR	AD8631ARTZ
AD8599ARZ	AD8609AR	AD8620BR	AD8632AR
AD8601ART	AD8609ARU	AD8622ARMZ	AD8632ARM
AD8602AR	AD8610AR	AD8622ARZ	AD8632ARMZ
AD8602ARM	AD8610ARM	AD8624ACPZ-R2	AD8632ARZ
AD8603AUJZ	AD8610ARZ	AD8624ARUZ	AD8634HRZN
AD8604AR	AD8610BR		AD8638ARJZ

Multisim 14.1 Education Components

AD8638ARZ	AD8656ARMZ	AD8669ARZ	AD9218_FP48
AD8639ACPZ-R2	AD8656ARZ	AD8671AR	AD9610TH
AD8639ARMZ	AD8657ACPZ-RL	AD8671ARM	AD9610TH/883B
AD8639ARZ	AD8657ARMZ	AD8671ARMZ	AD9617AQ
AD8639WARZ	AD8659ACPZ-R7	AD8672AR	AD9617BQ
AD8641AKSZ	AD8659ACPZ-RL	AD8672ARM	AD9617JN
AD8641AKSZ-R2	AD8659ARZ	AD8672ARMZ	AD9617JR
AD8641ARZ	AD8659ARZ-R7	AD8674AR	AD9617SQ
AD8642ARMZ	AD8659ARZ-RL	AD8674ARU	AD9617TQ
AD8642ARZ	AD8661ACPZ-R2	AD8675ARMZ	AD9618AQ
AD8643ACPZ-R2	AD8661ARZ	AD8675ARZ	AD9618BQ
AD8643ARZ	AD8662ARMZ	AD8676ARMZ	AD9618JN
AD8644AR	AD8662ARZ	AD8676ARZ	AD9618JR
AD8644ARU	AD8663ACPZ	AD8676BRMZ	AD9618SQ
AD8646ARMZ	AD8663ARZ	AD8676BRZ	AD9618TQ
AD8646ARZ	AD8664ARUZ	AD8677ARZ	AD9620AD
AD8646WARMZ-RL	AD8664ARZ	AD8677AUJZ-R2	AD9620SD
AD8646WARZ-RL	AD8665ARJZ-R2	AD8691AKSZ	AD9621AN
AD8648ARUZ	AD8665ARZ	AD8691AUJZ	AD9622AN
AD8648ARZ	AD8666ARMZ	AD8692ARMZ	AD9623AN
AD8648WARUZ	AD8666ARZ	AD8692ARZ	AD9624AN
AD8651AR	AD8666WARZ-R7	AD8694ARUZ	AD9630AN
AD8651ARM	AD8667ARMZ	AD8694ARZ	AD9630AQ
AD8655ARMZ	AD8667ARZ	AD8698AR	AD9630AR
AD8655ARZ	AD8669ARUZ	AD8698ARM	AD9631AN

Multisim 14.1 Education Components

AD9631AR	ADA4004-2ARZ-RL	ADA4077-2ARMZ-RL	ADA4091-4ARUZ
AD9632AN	ADA4004-4ACPZ-R2		ADA4092-4ARUZ
AD9632AR	ADA4004-4ACPZ-R7	ADA4077-2ARZ	ADA4096-2ACPZ-R7
ADA4000-1ARZ	ADA4004-4ACPZ-RL	ADA4077-2ARZ-R7	ADA4096-2ARMZ
ADA4000-1AUJZ	ADA4004-4ARZ	ADA4077-2ARZ-RL	ADA4096-2WARMZ-R7
ADA4000-1AUJZ-RL	ADA4004-4ARZ-R7	ADA4077-2BRZ	
ADA4000-2ARMZ	ADA4004-4ARZ-RL	ADA4077-2BRZ-R7	ADA4096-2WARMZ-RL
ADA4000-2ARZ	ADA4051-1AKSZ-R2	ADA4077-2BRZ-RL	ADA4096-4ACPZ-R7
ADA4000-4ARUZ	ADA4051-1ARJZ-R2	ADA4077-4ARUZ	ADA4096-4ARUZ
ADA4000-4ARZ	ADA4051-2ACPZ-R2	ADA4077-4ARZ	ADA4177-1ARMZ
ADA4001-2ARZ	ADA4051-2ARMZ	ADA4084-1ARJZ-R2	ADA4177-1ARZ
ADA4001-2ARZ-R7	ADA4062-2ACPZ-RL	ADA4084-1ARZ	ADA4177-2ARMZ
ADA4001-2ARZ-RL	ADA4062-2ARMZ	ADA4084-2ACPZ-R7	ADA4177-2ARZ
ADA4004-1ARJZ-R2	ADA4062-2ARZ	ADA4084-2ARMZ	ADA4177-4ARUZ
ADA4004-1ARJZ-R7	ADA4062-2BRZ	ADA4084-2ARMZ-R7	ADA4177-4ARZ
ADA4004-1ARJZ-RL	ADA4062-4ACPZ-R2	ADA4084-2ARMZ-RL	ADA4350ARUZ
ADA4004-1ARZ	ADA4062-4ARUZ		ADA4433-1BCPZ-R2
ADA4004-1ARZ-R7	ADA4075-2ACPZ-RL	ADA4084-2ARZ	ADA4433-1WBCPZ-R7
ADA4004-1ARZ-RL	ADA4075-2ARZ	ADA4084-2ARZ-R7	
ADA4004-2ARMZ	ADA4077-1ARMZ	ADA4084-2ARZ-RL	ADA4500-2ACPZ-R7
ADA4004-2ARMZ-R7	ADA4077-1ARZ	ADA4084-4ACPZ-R7	ADA4500-2ACPZ-RL
	ADA4077-1BRZ	ADA4084-4ARUZ	ADA4500-2ARMZ
ADA4004-2ARMZ-RL	ADA4077-2ARMZ	ADA4091-2ACPZ-R2	ADA4500-2ARMZ-R7
ADA4004-2ARZ	ADA4077-2ARMZ-R7	ADA4091-2ARZ	ADA4500-2ARMZ-RL
ADA4004-2ARZ-R7		ADA4091-4ACPZ-R2	

Multisim 14.1 Education Components

ADA4505-1ACBZ-R7	ADA4610-4ACPZ-R7	ADA4666-2ACPZ-R7	ADA4817-2ACPZ-R2
ADA4505-1ARJZ-R2	ADA4610-4ARZ	ADA4666-2ACPZ-RL	ADA4817-2ACPZ-R7
ADA4505-2ACBZ-RL	ADA4622-2ACPZ-R7	ADA4666-2ARMZ	ADA4817-2ACPZ-RL
ADA4505-2ARMZ	ADA4622-2ARMZ	ADA4666-2ARMZ-R7	ADA4841-1YRJZ-R2
ADA4505-4ACBZ-RL	ADA4622-2ARZ	ADA4666-2ARMZ-RL	ADA4841-1YRZ
ADA4505-4ARUZ	ADA4622-2BRZ		ADA4841-2YCPZ-R2
ADA4528-1ACPZ-R2	ADA4627-1ACPZ-RL	ADA4691-2ACBZ-R7	ADA4841-2YRMZ
ADA4528-1ARMZ	ADA4627-1ARZ	ADA4691-2ACPZ-R7	ADA4841-2YRZ
ADA4528-2ACPZ-R7	ADA4627-1BRZ	ADA4691-4ACPZ-R7	ADA4850-1YCPZ
ADA4528-2ARMZ	ADA4637-1ACPZ-R2	ADA4692-2ACPZ-R7	ADA4850-1YCPZ-R2
ADA4610-1ARJZ-R2	ADA4637-1ARZ	ADA4692-2ARZ	ADA4850-2YCPZ-R2
ADA4610-1ARZ	ADA4637-1BRZ	ADA4692-4ARUZ	ADA4850-2YCPZ-RL
ADA4610-1BRZ	ADA4638-1ACPZ-R7	ADA4700-1ARDZ	ADA4851-1WYRJZ-R7
ADA4610-2ACPZ-R7	ADA4638-1ACPZ-RL	ADA4805-1AKSZ-R2	ADA4851-1YRJZ-R2
ADA4610-2ACPZ-RL	ADA4638-1ARZ	ADA4805-1ARJZ-R2	ADA4851-1YRJZ-RL
ADA4610-2ARMZ	ADA4638-1ARZ-R7	ADA4805-2ACPZ-R2	ADA4851-2WYRMZ
ADA4610-2ARMZ-R7	ADA4638-1ARZ-RL	ADA4807-1AKSZ-R2	ADA4851-2YRMZ
ADA4610-2ARMZ-RL	ADA4661-2ACPZ-R7	ADA4807-1ARJZ-R2	ADA4851-2YRMZ-RL
	ADA4661-2ACPZ-RL	ADA4807-2ACPZ-R2	
ADA4610-2ARZ	ADA4661-2ARMZ	ADA4817-1ACPZ-R2	ADA4851-4WYRUZ
ADA4610-2ARZ-R7	ADA4661-2ARMZ-R7	ADA4817-1ACPZ-R7	ADA4851-4YRUZ
ADA4610-2ARZ-RL	ADA4661-2ARMZ-RL	ADA4817-1ACPZ-RL	ADA4851-4YRUZ-RL
ADA4610-2BRZ		ADA4817-1ARDZ	ADA4853-1AKSZ-R2
ADA4610-2BRZ-R7	ADA4665-2ARMZ	ADA4817-1ARDZ-R7	ADA4853-2YCPZ-R2
ADA4610-2BRZ-RL	ADA4665-2ARZ	ADA4817-1ARDZ-RL	

Multisim 14.1 Education Components

ADA4853-3WYCPZ-R7	ADA4895-1ARZ	ADA4922-1ARDZ	ADC16
ADA4853-3YCPZ-R2	ADA4895-2ARMZ	ADA4927-1YCPZ-R2	ADD_FULL
ADA4853-3YRUZ	ADA4895-2ARMZ-R7	ADA4927-2YCPZ	ADD_FULL4_FCR
ADA4855-3YCPZ-R2	ADA4895-2ARMZ-RL	ADA4930-1YCPZ-R2	ADD_HALF
ADA4857-1YCPZ-R2	ADA4896-2ACPZ-R2	ADA4930-2YCPZ-R2	ADG1211YCPZ-500RL7
ADA4857-1YRZ	ADA4896-2ACPZ-R7	ADA4932-1YCPZ-R2	ADG1211YRUZ
ADA4857-2YCPZ-R2	ADA4896-2ACPZ-RL	ADA4932-2YCPZ-R2	ADG1212YCPZ-500RL7
ADA4858-3ACPZ-R2	ADA4896-2ARMZ	ADA4937-1YCPZ-R2	ADG1212YRUZ
ADA4860-1YRJZ-R2	ADA4896-2ARMZ-R7	ADA4937-2YCPZ-R2	ADG1213YCPZ-500RL7
ADA4860-1YRJZ-RL	ADA4896-2ARMZ-RL	ADA4938-1ACPZ-R2	ADG1213YRUZ
ADA4860-1YRJZ-RL7	ADA4897-1ARJZ-R2	ADA4938-2ACPZ-R2	ADG1236YCPZ-500RL7
ADA4861-3YRZ	ADA4897-1ARZ	ADA4939-1YCPZ-R2	ADG1236YRUZ
ADA4861-3YRZ-RL	ADA4897-1SRJZ-EPR7	ADA4939-2YCPZ-R2	ADG1311YRUZ
ADA4861-3YRZ-RL7	ADA4897-2ARMZ	ADA4940-1ACPZ-R2	ADG1311YRZ
ADA4870ARRZ	ADA4897-2TRMZ-EP	ADA4940-1ACPZ-R7	ADG1312YRUZ
ADA4891-1ARJZ-R7	ADA4898-1YRDZ	ADA4940-2ACPZ-R2	ADG1312YRZ
ADA4891-1ARZ	ADA4898-2YRDZ	ADA4940-2ACPZ-RL	ADG1313YRUZ
ADA4891-2ARMZ	ADA4899-1YCPZ	ADA4941-1YCPZ-RL	ADG1313YRZ
ADA4891-2ARZ	ADA4899-1YCPZ-R2	ADA4941-1YRZ	ADG406BN
ADA4891-3ARUZ	ADA4899-1YRDZ	ADA4950-1YCPZ-R2	ADG406BP
ADA4891-3ARZ	ADA4922-1ACPZ-R2	ADA4950-2YCPZ-R2	ADG407BN
ADA4891-4ARUZ		ADA4960-1ACPZ-R2	ADG407BP
ADA4891-4ARZ		ADC	
ADA4895-1ARJZ-R2			

Multisim 14.1 Education Components

ADG408	ADG413BR	ADG509FBRN	ADG604YRU
ADG408BN	ADG413BRUZ	ADG509FBRUZ	ADG604YRUZ
ADG408BR	ADG413BRZ	ADG509FBRW	ADG608BN
ADG408BRU	ADG426BN	ADG509FBRWZ	ADG608BR
ADG408TQ	ADG426BRS	ADG509FTQ	ADG608BRU
ADG409BN	ADG441ABN	ADG511BN	ADG608TRU
ADG409BR	ADG441ABR	ADG511BR	ADG609BN
ADG409BRU	ADG441BN	ADG511PM5	ADG609BR
ADG409TQ	ADG441BR	ADG511TQ	ADG609BRU
ADG411	ADG441TQ	ADG512BN	ADG609BRUZ
ADG411BN	ADG442BN	ADG512BR	ADG609BRZ
ADG411BR	ADG442SQ	ADG512PM5	ADG611YRUZ
ADG411BRU	ADG444	ADG512TQ	ADG611YRZ
ADG411BRUZ	ADG444ABN	ADG513BN	ADG612WYRUZ- REEL
ADG411BRZ	ADG444ABR	ADG513BR	ADG612YRUZ
ADG411TQ	ADG444BN	ADG513PM5	ADG613YRUZ
ADG412	ADG444BR	ADG513TQ	ADG658YCPZ
ADG412BN	ADG444S	ADG528F	ADG658YRQ
ADG412BR	ADG508FBN	ADG528FBN	ADG658YRU
ADG412BRU	ADG508FBNZ	ADG528FBP	ADG659YCPZ
ADG412BRUZ	ADG508FBRN	ADG528FTQ	ADG659YRQ
ADG412BRZ	ADG508FBRUZ	ADG601BRMZ	ADG659YRU
ADG412TQ	ADG508FBRW	ADG601BRTZ-REEL	ADG663BRU
ADG413BN	ADG508FTQ	ADG602BRM	ADG701BRJ-500RL7
ADG413BNZ	ADG509FBN	ADG602BRTZ-REEL	

Multisim 14.1 Education Components

ADG701BRM	ADG723ACPZ-REEL	ADG819BCB	ADR5040BRTZ-R2
ADG701BRTZ-REEL	ADG723BRM	ADG819BRM	ADR5041AKSZ-R2
ADG701LBRJZ-REEL7	ADG741BKSZ5-REEL	ADG819BRT	ADR5041ARTZ-R2
ADG701LBRMZ	ADG741BKSZ-REEL	ADG820BRM	ADR5041BKSZ-R2
ADG701LBRTZ-REEL7	ADG742BKSZ5-REEL	ADG820BRT	ADR5041BRTZ-R2
ADG702BRJ-REEL7	ADG742BKSZ-R2	ADG821BRM	ADR5041WARTZ-R7
ADG702BRM	ADG749BKSZ-REEL	ADG822BRM	ADR5041WBRTZ-R7
ADG702BRTZ-REEL	ADG779BKSZ-R2	ADG823BRM	ADS8320EB
ADG702LBRJ-REEL	ADG781BCP	ADG839YKSZ-500RL7	ADS8322YB
ADG702LBRMZ	ADG782BCP	ADG841YKSZ-500RL7	ADS8364Y
ADG702LBRTZ-REEL7	ADG783BCP	ADG842YKSZ-500RL7	ADTL082ARMZ
ADG711BR	ADG787BCBZ-REEL	ADG849YKSZ-500RL7	ADTL082ARZ
ADG711BRU	ADG787BCPZ-REEL	ADG859YKSZ-500RL7	ADTL082JR
ADG712BR	ADG787BRMZ	ADG859BRYZ-REEL	ADTL082JRZ
ADG712BRU	ADG801BRM	ADG859YRYZ-REEL	ADTL084ARUZ
ADG713BR	ADG801BRT-500RL7	ADG884BCBZ-REEL	ADTL084ARZ
ADG713BRU	ADG802BCBZ-REEL7	ADG884BCPZ-REEL	ADTL084JR
ADG719BRM	ADG802BRM	ADG884BRMZ	ADTL084JRZ
ADG719BRT-REEL	ADG802BRT-500RL7	ADR3425ARJZ-R2	ADZS-BRKOUT-EX3
ADG721ACPZ-REEL	ADG811YCPZ-REEL	ADR3425ARJZ-R7	AIR_NC
ADG721BRM	ADG811YRU	ADR5040AKSZ-R2	AIR_NO
ADG722ACPZ-REEL	ADG812YRU	ADR5040ARTZ-R2	A-jB_BLOCK
ADG722BRM	ADG813YRU	ADR5040BKSZ-R2	ALM2402QDRRRQ1
			ALM2402QPWPRQ1

Multisim 14.1 Education Components

ALPHA_NUMERIC_COM_A_BLUE	AMC1301DWV	ANALOG_SWITCH_VIRTUAL	ARBITRARY_LOGIC_BLOCK_8_8
ALPHA_NUMERIC_COM_A_GREEN	AMMETER_H	AND_OR_I	ARBITRARY_SPICE_BLOCK
ALPHA_NUMERIC_COM_A_ORANGE	AMMETER_HR	AND2	ARM-14-HDR
ALPHA_NUMERIC_COM_A_RED	AMMETER_V	AND2	ARM-20-HDR
ALPHA_NUMERIC_COM_A_YELLOW	AMMETER_VR	AND3	ASP-134488-01
ALPHA_NUMERIC_COM_K_BLUE	AMP01AX	AND3	ASP-134603-01
ALPHA_NUMERIC_COM_K_GREEN	AMP01BX	AND4	ASP-134604-01
ALPHA_NUMERIC_COM_K_ORANGE	AMP01EX	AND4	ASP-134606-01
ALPHA_NUMERIC_COM_K_RED	AMP01FX	AND5	ASSR-V621-002E
ALPHA_NUMERIC_COM_K_YELLOW	AMP01GS	AND5	ASSR-V621-302E
ALTERA-BYTEBLASTER-HDR	AMP02AZ	AND6	ASSR-V622-002E
ALU_4BIT	AMP02EP	AND6	ASSR-V622-302E
AM_VOLTAGE	AMP02ES	AND7	ATP101-TL-H
AM29705DC	AMP02FP	AND7	ATP102-TL-H
AM29705PC	AMP02FS	AND8	ATP103-TL-H
AMC1200BDUB	AMP04EP	AND8	ATP104-TL-H
AMC1200BDWV	AMP04ES	ANGLE_WRAP	ATP106-TL-H
AMC1200SDUB	AMP04FP	ANTI_PLUG	ATP107-TL-H
	AMP04FS	ARBITRARY_LAPLACE_FUNCTION	ATP108-TL-H
	AMPSIMP	ARBITRARY_LOAD	ATP112-TL-H
	ANALOG_AND	ARBITRARY_LOGIC_BLOCK_16_16	ATP113-TL-H
	ANALOG_INV		ATP114-TL-H
	ANALOG_OR	ARBITRARY_LOGIC_BLOCK_4_4	ATP202-TL-H
	ANALOG_SR_LATCH		ATP207-TL-H

Multisim 14.1 Education Components

ATP212-TL-H	AUIRFR4292TRR	AUIRGR4045DTR	BA423L
ATP301-TL-H	AUIRFR8401	AUIRGR4045DTRL	BA481
ATP304-TL-H	AUIRFR8405	AUIRGR4045DTRR	BA482
ATP405-TL-H	AUIRFS6535	AUIRGU4045D	BA483
ATP613-TL-H	AUIRFS6535TRL	AUIRLS3034-7P	BA484
AUIRF2903ZL	AUIRFS8403	AUIRLS3034-7TRL	BA592
AUIRF2903ZS	AUIRFS8405	AUIRLS3036-7P	BA595
AUIRF3004WL	AUIRFS8407	AUIRLS3114Z	BA682
AUIRF7303QTR	AUIRFS8407TRL	AUIRLS3114ZTRL	BA683
AUIRF7313Q	AUIRFS8408	AVR-JTAG-HDR	BA885
AUIRF7640S2TR	AUIRFS8408TRL	B6S-E3/80	BA892
AUIRF7647S2TR	AUIRFS8408TRR	BA157GP	BA895
AUIRF7648M2TR	AUIRFSL6535	BA158GP	BAL74
AUIRF7669L2TR	AUIRFSL8408	BA159-E3/54	BAL99
AUIRF7734M2TR	AUIRFU4292	BA159GP	BAR_LED_BLUE
AUIRF7736M2TR	AUIRFZ44VZS	BA220	BAR_LED_BLUE_FOUR
AUIRF7737L2TR	AUIRGDC0250	BA221	BAR_LED_BLUE_TEN
AUIRF7738L2TR	AUIRGP4063D	BA223	BAR_LED_BLUE_TEN
AUIRF7739L2TR	AUIRGP4063D-E	BA281	BAR_LED_GREEN
AUIRF7749L2	AUIRGP4066D1	BA314	BAR_LED_GREEN_FOUR
AUIRF8736M2	AUIRGP4066D1-E	BA315	BAR_LED_GREEN_TEN
AUIRFN7110	AUIRGP50B60PD1	BA316	BAR_LED_GREEN_TEN
AUIRFP4310Z	AUIRGP50B60PD1E	BA317	BAR_LED_ORANGE
AUIRFR4292	AUIRGPS4067D1	BA318	BAR_LED_ORANGE
AUIRFR4292TRL	AUIRGR4045D	BA423	_FOUR

Multisim 14.1 Education Components

BAR_LED_ORANGE_TEN	BAR63-06W	BAS125-07W	BAS21AW
BAR_LED_RED	BAR64-02V	BAS140W	BAS21H
BAR_LED_RED_FOUR	BAR64-03W	BAS15	BAS21HT1G
BAR_LED_RED_TEN	BAR64-04	BAS16	BAS21J
BAR_LED_YELLOW	BAR64-04W	BAS16-02L	BAS21M3T5G
BAR_LED_YELLOW_FOUR	BAR64-05W	BAS16DXV6T1G	BAS21SLT1G
BAR_LED_YELLOW_TEN	BAR64-06W	BAS16H	BAS21SW
BAR14-1	BAR65-03W	BAS16J	BAS21TMR6T1G
BAR15-1	BAR67-02V	BAS16L	BAS21U
BAR16-1	BAR74	BAS16LD	BAS21VD
BAR50-02L	BAR81W	BAS16M3T5G	BAS21W
BAR50-02V	BAR88-02V	BAS16P2T5G	BAS28
BAR61	BAR99	BAS16QA	BAS29
BAR63-02L	BAS101	BAS16T	BAS3010B-03W
BAR63-02V	BAS101S	BAS16VV	BAS3020B
BAR63-02W	BAS11	BAS16VY	BAS31
BAR63-03W	BAS116	BAS16W	BAS316
BAR63-04	BAS116H	BAS17	BAS32
BAR63-04W	BAS116L	BAS170W	BAS321
BAR63-05	BAS116LT1G	BAS19	BAS32L
BAR63-05W	BAS116QA	BAS20	BAS35
BAR63-06	BAS116T	BAS20HT1G	BAS40
	BAS116TT1G	BAS20LT1G	BAS40-02L
	BAS125-04W	BAS21	BAS40-04
	BAS125-05W	BAS21AVD	BAS40-05

Multisim 14.1 Education Components

BAS40-05V	BAS70-05	BAT15_099	BAT54
BAS40-05W	BAS70-05W	BAT15_099R	BAT54A
BAS40-06	BAS70-06	BAT15-02LRH	BAT54AW
BAS40-06W	BAS70-06W	BAT15-03W	BAT54C
BAS40-07	BAS70-07	BAT15-04W	BAT54CLT1
BAS40-07V	BAS70-07S	BAT15-05W	BAT54CLT1G
BAS40-07W	BAS70-07V	BAT15-099	BAT54CLT3G
BAS40H	BAS70H	BAT160A	BAT54CM
BAS40L	BAS70L	BAT160C	BAT54CV
BAS40W	BAS70VV	BAT160S	BAT54CW
BAS40XY	BAS70W	BAT165	BAT54H
BAS416	BAS70XY	BAT165A	BAT54J
BAS45	BAS716	BAT17	BAT54L
BAS45A	BAS81	BAT17-04	BAT54LT1G
BAS45AL	BAS82	BAT17-05	BAT54M3T5G
BAS45L	BAS83	BAT17-05W	BAT54S
BAS516	BAS85	BAT17-06W	BAT54SW
BAS521	BAS86	BAT17-07	BAT54T
BAS56	BAT120A	BAT18	BAT54VV
BAS70	BAT120C	BAT18-04	BAT54W
BAS70-02L	BAT120S	BAT18-05	BAT54WT1G
BAS70-02W	BAT14_098	BAT24-02LS	BAT54XY
BAS70-04	BAT15_03W	BAT240A	BAT60A
BAS70-04LT1G	BAT15_04	BAT46WH	BAT60B
BAS70-04W	BAT15_098	BAT46WJ	BAT62

Multisim 14.1 Education Components

BAT62-02L	BAT721S	BAV105	BAV70TT1G
BAT62-02W	BAT74	BAV170	BAV70W
BAT62-03W	BAT74S	BAV170M	BAV74
BAT62-07W	BAT74V	BAV170QA	BAV74LT1
BAT63	BAT754	BAV18	BAV74LT1G
BAT63-07W	BAT754A	BAV19	BAV756S
BAT64	BAT754C	BAV199	BAV99
BAT64-02W	BAT754L	BAV199W	BAV99LT1
BAT64-04	BAT754S	BAV20	BAV99LT1G
BAT64-04W	BAT760	BAV21	BAV99LT3
BAT64-05	BAT81	BAV23	BAV99LT3G
BAT64-05W	BAT82	BAV23A	BAV99QA
BAT64-06	BAT83	BAV23C	BAV99S
BAT64-06W	BAT85	BAV23S	BAV99W
BAT65	BAT854AW	BAV45	BAW101
BAT66-05	BAT854CW	BAV70	BAW101S
BAT68	BAT854SW	BAV70DXV6T5G	BAW156
BAT68-04	BAT854W	BAV70LT1	BAW56
BAT68-04W	BAT86	BAV70LT1G	BAW56LT1
BAT68-06	BAT960	BAV70LT3G	BAW56LT1G
BAT68-06W	BAV10	BAV70M	BAW56LT3G
BAT720	BAV100	BAV70M3T5G	BAW56M
BAT721	BAV101	BAV70QA	BAW56M3T5G
BAT721A	BAV102	BAV70S	BAW56QA
BAT721C	BAV103	BAV70T	BAW56S

Multisim 14.1 Education Components

BAW56T	BB545	BB909A	BBY57-02W
BAW56TT1G	BB555	BB909B	BBY57-05W
BAW56W	BB555-02V	BB910	BBY58-02V
BAW62	BB565	BB911	BBY58-02W
BAW78D	BB565-02V	BB914	BBY58-03W
BAX12	BB619	BBS3002-DL-1E	BBY58-05W
BAX14	BB620	BBS3002-TL-1E	BBY58-06W
BAX18	BB639	BBY31	BBY62
BAY80	BB639C	BBY39	BBY65-02V
BB112	BB640	BBY40	BBY66-02V
BB119	BB644	BBY42	BBY66-05W
BB130	BB659	BBY51-02W	BC107BP
BB204B	BB659C	BBY51-03W	BC108BP
BB204G	BB659C-02V	BBY52-02L	BC109BP
BB212	BB664	BBY52-02W	BC177AP
BB215	BB664-02V	BBY53-02L	BC178AP
BB219	BB689	BBY53-02V	BC182BP
BB240	BB689-02V	BBY53-02W	BC183BP
BB241	BB804	BBY53-03W	BC184BP
BB249	BB809	BBY53-05W	BC212AP
BB405B	BB811	BBY55-02V	BC213AP
BB417	BB814	BBY55-03W	BC237BP
BB439	BB833	BBY56-02W	BC238BP
BB515	BB837	BBY56-03W	BC239BP
BB535	BB857	BBY57-02V	BC264A

Multisim 14.1 Education Components

BC264B	BC52-16PA	BC55-10PAS	BC68-25PA
BC264C	BC52-16PAS	BC55-16PA	BC68-25PAS
BC264D	BC52PA	BC55-16PAS	BC68PA
BC307AP	BC52PAS	BC556AP	BC68PAS
BC308AP	BC53-10PA	BC557AP	BC69-16PA
BC327	BC53-10PAS	BC557BG	BC69-16PAS
BC328	BC53-16PA	BC557BRL1G	BC69-25PA
BC337	BC53-16PAS	BC557BZL1G	BC69-25PAS
BC337AP	BC53PA	BC558AP	BC69PA
BC338	BC53PAS	BC559AP	BC69PAS
BC338AP	BC54-10PA	BC55PA	BC807
BC368	BC54-10PAS	BC55PAS	BC807-16
BC369	BC54-16PA	BC560AP	BC807-16LT1G
BC413BP	BC54-16PAS	BC56-10PA	BC807-16LT3G
BC414BP	BC546BP	BC56-10PAS	BC807-16W
BC415AP	BC547BG	BC56-16PA	BC807-25
BC416AP	BC547BP	BC56-16PAS	BC807-25LT1G
BC51-10PA	BC547BRL1G	BC56PA	BC807-25LT3G
BC51-10PAS	BC547BZL1G	BC56PAS	BC807-25QA
BC51-16PA	BC548BP	BC635	BC807-25W
BC51-16PAS	BC549BP	BC636	BC807-40
BC51PA	BC54PA	BC637	BC807-40LT1G
BC51PAS	BC54PAS	BC638	BC807-40LT3G
BC52-10PA	BC550BP	BC639	BC807-40QA
BC52-10PAS	BC55-10PA	BC640	BC807-40W

Multisim 14.1 Education Components

BC807DS	BC846ALT1G	BC847AT	BC847CT
BC807W	BC846ALT3G	BC847AW	BC847CTT1G
BC808-16	BC846AT	BC847B	BC847CW
BC808-25	BC846AW	BC847BDW1T1G	BC847DS
BC808-40	BC846B	BC847BDW1T3	BC847QAPN
BC817	BC846BDW1T1G	BC847BDW1T3G	BC847QAS
BC817-16	BC846BLT1G	BC847BM	BC847T
BC817-16W	BC846BLT3G	BC847BMB	BC847W
BC817-25	BC846BM	BC847BPDW1T1	BC848
BC817-25LT1	BC846BM3T5G	BC847BPDW1T1G	BC848A
BC817-25LT1G	BC846BMB	BC847BPDW1T2G	BC848B
BC817-25LT3G	BC846BPDW1T1G	BC847BPDW1T3G	BC848BW
BC817-25QA	BC846BPN	BC847BPDV6T1G	BC848CW
BC817-25W	BC846BS	BC847BPN	BC848W
BC817-40	BC846BT	BC847BQA	BC849B
BC817-40QA	BC846BW	BC847BS	BC849BW
BC817-40W	BC846DS	BC847BT	BC849C
BC817DPN	BC846S	BC847BV	BC849CW
BC817DS	BC846T	BC847BVN	BC850B
BC817W	BC846W	BC847BW	BC850BW
BC818-16	BC847	BC847C	BC850C
BC818-25	BC847A	BC847CDV6T1G	BC850CW
BC818-40	BC847AM	BC847CM	BC856
BC846	BC847AMB	BC847CMB	BC856A
BC846A	BC847AQA	BC847CQA	BC856ALT1G

Multisim 14.1 Education Components

BC856AT	BC857BQA	BC859C	BCP51
BC856AW	BC857BS	BC859CW	BCP51-10
BC856B	BC857BT	BC860A	BCP51-16
BC856BDW1T1G	BC857BV	BC860B	BCP52
BC856BDW1T3G	BC857BW	BC860BW	BCP52-10
BC856BM	BC857C	BC860C	BCP52-16
BC856BMB	BC857CM	BC860CW	BCP53
BC856BS	BC857CMB	BC868	BCP53-10
BC856BT	BC857CQA	BC868-25	BCP53-16
BC856BW	BC857CT	BC869	BCP54
BC856BWT1G	BC857CW	BC869-16	BCP54-10
BC856S	BC857QAS	BC869-25	BCP54-16
BC856T	BC857T	BCD_7SEG_DCD	BCP55
BC856W	BC857W	BCM61B	BCP55-10
BC857	BC858	BCM62B	BCP55-16
BC857A	BC858A	BCM846BS	BCP56
BC857AM	BC858AW	BCM847BS	BCP56-10
BC857AMB	BC858B	BCM847BV	BCP56-10T1
BC857AQA	BC858BW	BCM847DS	BCP56-10T1G
BC857AT	BC858C	BCM856BS	BCP56-10T3G
BC857AW	BC858CW	BCM856DS	BCP56-16
BC857B	BC858W	BCM857BS	BCP56-16T1
BC857BDW1T1G	BC859A	BCM857BV	BCP56-16T1G
BC857BM	BC859B	BCM857DS	BCP56-16T3G
BC857BMB	BC859BW	BCP49	BCP56T1

Multisim 14.1 Education Components

BCP56T1G	BCR133	BCR183W	BCR562
BCP56T3G	BCR133S	BCR185	BCR573
BCP68	BCR133W	BCR185S	BCR583
BCP68-25	BCR135	BCR185W	BCV26
BCP68T1G	BCR135S	BCR191	BCV27
BCP69	BCR135W	BCR191W	BCV28
BCP69-16	BCR141	BCR192	BCV29
BCP69-25	BCR141S	BCR192W	BCV46
BCP69T1G	BCR141W	BCR196	BCV47
BCR08PN	BCR142	BCR196W	BCV48
BCR108	BCR142W	BCR198	BCV49
BCR108S	BCR146	BCR198S	BCV61
BCR108W	BCR148	BCR198W	BCV61A
BCR10PN	BCR148S	BCR22PN	BCV61B
BCR112	BCR148W	BCR35PN	BCV61C
BCR112W	BCR158	BCR48PN	BCV62
BCR116	BCR158W	BCR503	BCV62A
BCR116S	BCR162	BCR505	BCV62B
BCR116W	BCR166	BCR512	BCV62C
BCR119	BCR166W	BCR521	BCV63
BCR119S	BCR169	BCR523	BCV63B
BCR119W	BCR169S	BCR523U	BCV64B
BCR129	BCR169W	BCR533	BCV65
BCR129S	BCR183	BCR553	BCV71
BCR129W	BCR183S	BCR555	BCV72

Multisim 14.1 Education Components

BCW29	BCW68F	BCX54-16	BD135-16
BCW30	BCW69	BCX55	BD135G
BCW31	BCW70	BCX55-10	BD136
BCW32	BCW71	BCX55-16	BD136G
BCW33	BCW72	BCX56	BD137
BCW60A	BCW89	BCX56-10	BD137G
BCW60B	BCX17	BCX56-16	BD138
BCW60C	BCX17_25	BCX58IX	BD138G
BCW60D	BCX17LT1G	BCX58VIII	BD139
BCW60FF	BCX18	BCX58X	BD139G
BCW60FN	BCX19	BCX59IX	BD140
BCW61A	BCX38B	BCX59VIII	BD140G
BCW61B	BCX41	BCX59X	BD159G
BCW61C	BCX42	BCX68	BD179G
BCW61D	BCX51	BCX69	BD180G
BCW61FF	BCX51-10	BCX70G	BD234G
BCW61FN	BCX51-16	BCX70H	BD237G
BCW65A	BCX52	BCX70J	BD241CG
BCW65B	BCX52-10	BCX70K	BD242BG
BCW65C	BCX52-16	BCX71G	BD242CG
BCW66F	BCX53	BCX71H	BD243CG
BCW66G	BCX53-10	BCX71J	BD244BG
BCW66H	BCX53-16	BCX71K	BD244CG
BCW67A	BCX54	BD135	BD329
BCW68	BCX54-10	BD135-10	BD330

Multisim 14.1 Education Components

BD436TG	BD810G	BF247A	BF545C
BD437G	BDP947	BF256A	BF550
BD437TG	BDP948	BF256B	BF556A
BD438G	BDP949	BF370R	BF556B
BD439G	BDP950	BF410A	BF570
BD440G	BDP953	BF410B	BF603
BD441G	BDP954	BF410C	BF620
BD442G	BDV64BG	BF410D	BF621
BD675AG	BDV65BG	BF420	BF622
BD675G	BDW42G	BF421	BF623
BD676AG	BDW46G	BF422	BF720
BD676G	BDW47G	BF422G	BF721
BD677AG	BDX33BG	BF423	BF722
BD677G	BDX33CG	BF450	BF723
BD678AG	BDX34BG	BF469	BF799
BD678G	BDX34CG	BF470	BF799W
BD679AG	BDX53BG	BF471	BF820
BD679G	BDX53CG	BF472	BF820W
BD680AG	BDX54BG	BF510	BF821
BD680G	BDX54CG	BF511	BF822
BD681G	BF240	BF512	BF822W
BD682G	BF245A	BF513	BF823
BD787G	BF245B	BF517	BF824
BD788G	BF245C	BF545A	BF824W
BD809G	BF246A	BF545B	BF840

Multisim 14.1 Education Components

BF851A	BFN17	BFP193W	BFP650
BF851B	BFN18	BFP194	BFP720
BF851C	BFN19	BFP196	BFP720ESD
BF861A	BFN21	BFP196W	BFP720F
BF861B	BFN22	BFP22	BFP720FESD
BF861C	BFN23	BFP23	BFP740
BF869	BFN24	BFP25	BFP740ESD
BF871	BFN25	BFP26	BFP740F
BF904	BFN26	BFP280	BFP740FESD
BF904R	BFN27	BFP280W	BFP760
BF904WR	BFN36	BFP405	BFP81
BF908WR	BFN37	BFP420	BFP840ESD
BF909	BFN38	BFP450	BFP840FESD
BF909R	BFN39	BFP460	BFP842ESD
BF909WR	BFP 183 E7764	BFP490	BFP843
BF998	BFP136W	BFP520	BFP843F
BF998R	BFP180	BFP540	BFP93A
BF998WR	BFP180W	BFP540ESD	BFQ31
BFG135A	BFP181	BFP540FESD	BFQ81
BFG193	BFP181W	BFP620	BFR106
BFG194	BFP182	BFP620F	BFR180
BFG196	BFP182W	BFP640	BFR180W
BFG19S	BFP183	BFP640ESD	BFR181
BFG235	BFP183W	BFP640F	BFR181W
BFN16	BFP193	BFP640FESD	BFR182

Multisim 14.1 Education Components

BFR182W	BFS17	BFW61	BPV10NF
BFR183	BFS17H	BICOLOR_LED_Red/ Green	BPV22NF
BFR183W	BFS17LT1		BPV23F
BFR193	BFS17P	BICOLOR_LED_Red- Orange/Green	BPV23NF
BFR193F	BFS17S	BIPOLAR_CURRENT	BPW 34
BFR193W	BFS17W	BIPOLAR_VOLTAGE	BPW 34 FA
BFR194	BFS18	BJT_LPNP	BPW 34 FAS
BFR280	BFS19	BJT_NPN	BPW 34 FASR
BFR280W	BFS20	BJT_NPN_4T	BRUSHLESS_DC_M ACHINE
BFR30	BFS20W	BJT_NPN_RATED	BRUSHLESS_DC_M ACHINE_HALL
BFR31	BFS480	Bjt_npn1	
BFR340F	BFS481	BJT_PNP	BS170
BFR340L3	BFS482	BJT_PNP_4T	BSB008NE2LX
BFR35AP	BFS483	BJT_PNP_RATED	BSB012N03LX3 G
BFR360F	BFS60	Bjt-pnp1	BSB012NE2LX
BFR380F	BFT46	BMS3003-1E	BSB012NE2LXI
BFR460L3	BFT92	BOOST_CONVERTE R	BSB013NE2LXI
BFR740L3RH	BFT92W		BSB014N04LX3 G
BFR840L3RHESD	BFU308	BOOSTCCM	BSB015N04NX3 G
BFR92ALT1	BFU309	BOOSTCM	BSB017N03LX3 G
BFR92P	BFU310	BOOSTDCM	BSB028N06NN3 G
BFR92W	BFW10	BOOSTVM	BSB044N08NN3 G
BFR93A	BFW11	BOSCH-EDC16- BDM-HDR	BSB056N10NN3 G
BFR93ALT1	BFW12		BSB165N15NZ3 G
BFR93AW	BFW13	BPASS	BSB280N15NZ3 G

Multisim 14.1 Education Components

BSC009NE2LS	BSC019N04LS	BSC035N10NS5	BSC061N08NS5
BSC009NE2LS5	BSC019N04NS G	BSC036NE7NS3 G	BSC066N06NS
BSC009NE2LS5I	BSC020N03LS G	BSC037N08NS5	BSC067N06LS3 G
BSC010N04LS	BSC020N03MS G	BSC039N06NS	BSC070N10NS3 G
BSC010N04LSI	BSC022N04LS	BSC040N08NS5	BSC070N10NS5
BSC010NE2LS	BSC024NE2LS	BSC040N10NS5	BSC072N03LD G
BSC010NE2LSI	BSC025N03LS G	BSC042N03LS G	BSC072N08NS5
BSC011N03LS	BSC025N03MS G	BSC042N03MS G	BSC076N06NS3 G
BSC011N03LSI	BSC026N02KS G	BSC042NE7NS3 G	BSC077N12NS3 G
BSC014N03LS G	BSC026N04LS	BSC046N02KS G	BSC079N10NS G
BSC014N03MS G	BSC026N08NS5	BSC046N10NS3 G	BSC080N03LS G
BSC014N04LS	BSC026NE2LS5	BSC047N08NS3 G	BSC080N03MS G
BSC014N04LSI	BSC027N04LS G	BSC050N03LS G	BSC080P03LS G
BSC014N06NS	BSC028N06LS3 G	BSC050N03MS G	BSC082N10LS G
BSC014NE2LSI	BSC028N06NS	BSC050N04LS G	BSC084P03NS3 G
BSC015NE2LS5I	BSC030N03LS G	BSC050NE2LS	BSC084P03NS3E G
BSC016N03LS G	BSC030N03MS G	BSC052N03LS	BSC0901NS
BSC016N03MS G	BSC030N04NS G	BSC052N08NS5	BSC0901NSI
BSC016N04LS G	BSC030N08NS5	BSC054N04NS G	BSC0902NS
BSC016N06NS	BSC030P03NS3 G	BSC057N03LS G	BSC0902NSI
BSC017N04NS G	BSC031N06NS3 G	BSC057N03MS G	BSC0904NSI
BSC018N04LS G	BSC032N04LS	BSC057N08NS3 G	BSC0906NS
BSC018NE2LS	BSC032NE2LS	BSC059N04LS G	BSC0908NS
BSC018NE2LSI	BSC034N06NS	BSC060N10NS3 G	BSC0909NS
BSC019N02KS G	BSC035N04LS G	BSC060P03NS3E G	BSC090N03LS G

Multisim 14.1 Education Components

BSC090N03MS G	BSC150N03LD G	BSD215	BSH201
BSC0910NDI	BSC152N10NSF G	BSD223P	BSH202
BSC0911ND	BSC159N10LSF G	BSD235C	BSH203
BSC0921NDI	BSC160N10NS3 G	BSD235N	BSH205
BSC0923NDI	BSC16DN25NS3 G	BSD314SPE	BSH207
BSC0924NDI	BSC190N12NS3 G	BSD316SN	BSJ108
BSC0925ND	BSC190N15NS3 G	BSD816SN	BSJ109
BSC093N04LS G	BSC196N10NS G	BSD840N	BSJ110
BSC097N06NS	BSC200P03LS G	BSE-080-01-L-D-A	BSL202SN
BSC098N10NS5	BSC205N10LS G	BSF024N03LT3 G	BSL205N
BSC100N03LS G	BSC22DN20NS3 G	BSF030NE2LQ	BSL207N
BSC100N03MS G	BSC240N12NS3 G	BSF035NE2LQ	BSL207SP
BSC100N06LS3 G	BSC252N10NSF G	BSF050N03LQ3 G	BSL211SP
BSC100N10NSF G	BSC265N10LSF G	BSF134N10NJ3 G	BSL214N
BSC105N10LSF G	BSC320N20NS3 G	BSF450NE7NH3 G	BSL215C
BSC109N10NS3 G	BSC340N08NS3 G	BSG0810NDI	BSL296SN
BSC110N06NS3 G	BSC360N15NS3 G	BSG0811ND	BSL302SN
BSC117N08NS5	BSC440N10NS3 G	BSG0813NDI	BSL303SPE
BSC118N10NS G	BSC500N20NS3 G	BSH103	BSL305SPE
BSC120N03LS G	BSC520N15NS3 G	BSH105	BSL306N
BSC120N03MS G	BSC600N25NS3 G	BSH108	BSL307SP
BSC123N08NS3 G	BSC750N10ND G	BSH111	BSL308C
BSC123N10LS G	BSC900N20NS3 G	BSH111BK	BSL308PE
BSC12DN20NS3 G	BSD214	BSH114	BSL314PE
BSC130P03LS G	BSD214SN	BSH121	BSL316C

Multisim 14.1 Education Components

BSL372SN	BSO150N03MD G	BSP130	BSP315
BSL373SN	BSO200P03S H	BSP135	BSP315P
BSL606SN	BSO201SP H	BSP149	BSP316
BSL716SN	BSO203P H	BSP16T1G	BSP316P
BSL802SN	BSO203SP H	BSP170P	BSP317
BSL806N	BSO207P H	BSP171P	BSP317P
BSN011NE2LS	BSO211P H	BSP19	BSP318S
BSN011NE2LSI	BSO220N03MD G	BSP19AT1G	BSP319
BSN012N03LS	BSO220N03MS G	BSP204	BSP32
BSN012N03LSI	BSO301SP H	BSP204A	BSP320S
BSN045NE2LS	BSO303P H	BSP205	BSP321P
BSN048N03LS	BSO303SP H	BSP206	BSP322P
BSN20	BSO330N02K G	BSP220	BSP324
BSN20BK	BSO612CV G	BSP225	BSP33
BSO033N03MS G	BSO613SPV G	BSP230	BSP372N
BSO040N03MS G	BSO615C G	BSP250	BSP373N
BSO051N03MS G	BSP 60 E6327	BSP295	BSP41
BSO065N03MS G	BSP030	BSP296	BSP43
BSO080P03NS3 G	BSP100	BSP296N	BSP50
BSO080P03NS3E G	BSP110	BSP297	BSP51
BSO080P03S H	BSP122	BSP299	BSP52
BSO083N03MS G	BSP123	BSP300	BSP52T1G
BSO110N03MS G	BSP125	BSP304	BSP52T3G
BSO130N03MS G	BSP126	BSP304A	BSP60
BSO130P03S H	BSP129	BSP31	BSP61

Multisim 14.1 Education Components

BSP613P	BSS100	BSS139	BSS670S2L
BSP62	BSS101	BSS145	BSS7728N
BSP716N	BSS110	BSS159N	BSS79B
BSP88	BSS119	BSS169	BSS79C
BSP89	BSS119N	BSS192	BSS806N
BSP92P	BSS123	BSS192P	BSS80B
BSR13	BSS123LT1G	BSS205N	BSS80C
BSR14	BSS123N	BSS209PW	BSS816NW
BSR16	BSS125	BSS214N	BSS81B
BSR19A	BSS126	BSS214NW	BSS81C
BSR202N	BSS127	BSS215P	BSS82B
BSR30	BSS129	BSS223PW	BSS82C
BSR302N	BSS131	BSS225	BSS83
BSR31	BSS135	BSS229	BSS83P
BSR315P	BSS138	BSS295	BSS84
BSR316P	BSS138BK	BSS296	BSS84AK
BSR33	BSS138BKS	BSS297	BSS84AKM
BSR41	BSS138BKW	BSS306N	BSS84AKMB
BSR43	BSS138LT1G	BSS308PE	BSS84AKS
BSR56	BSS138LT3G	BSS314PE	BSS84AKT
BSR57	BSS138N	BSS315P	BSS84AKV
BSR58	BSS138P	BSS316N	BSS84AKW
BSR606N	BSS138PS	BSS606N	BSS84LT1G
BSR802N	BSS138PW	BSS63	BSS84P
BSR92P	BSS138W	BSS64	BSS84PW

Multisim 14.1 Education Components

BSS84PW H6327	BSZ014NE2LS5IF	BSZ075N08NS5	BSZ120P03NS3E G
BSS87	BSZ017NE2LS5I	BSZ076N06NS3 G	BSZ123N08NS3 G
BSS88	BSZ018NE2LS	BSZ084N08NS5	BSZ12DN20NS3 G
BSS89	BSZ018NE2LSI	BSZ086P03NS3 G	BSZ130N03LS G
BSS92	BSZ019N03LS	BSZ086P03NS3E G	BSZ130N03MS G
BSS98	BSZ023N04LS	BSZ088N03LS G	BSZ150N10LS3 G
BST100	BSZ025N04LS	BSZ088N03MS G	BSZ15DC02KD H
BST110	BSZ028N04LS	BSZ0901NS	BSZ160N10NS3 G
BST120	BSZ031NE2LS5	BSZ0901NSI	BSZ165N04NS G
BST122	BSZ033NE2LS5	BSZ0902NS	BSZ16DN25NS3 G
BST39	BSZ034N04LS	BSZ0902NSI	BSZ180P03NS3 G
BST50	BSZ035N03LS G	BSZ0904NSI	BSZ180P03NS3E G
BST51	BSZ035N03MS G	BSZ0907ND	BSZ22DN20NS3 G
BST52	BSZ036NE2LS	BSZ0908ND	BSZ240N12NS3 G
BST60	BSZ040N04LS G	BSZ0909NS	BSZ340N08NS3 G
BST61	BSZ042N04NS G	BSZ097N04LS G	BSZ42DN25NS3 G
BST62	BSZ042N06NS	BSZ097N10NS5	BSZ440N10NS3 G
BST82	BSZ050N03LS G	BSZ100N03LS G	BSZ520N15NS3 G
BSV236SP	BSZ050N03MS G	BSZ100N03MS G	BSZ900N15NS3 G
BSV52	BSZ058N03LS G	BSZ100N06LS3 G	BSZ900N20NS3 G
BSV78	BSZ058N03MS G	BSZ100N06NS	BT134
BSV79	BSZ060NE2LS	BSZ105N04NS G	BT134-E
BSV80	BSZ065N03LS	BSZ110N06NS3 G	BT134-F
BSV81	BSZ067N06LS3 G	BSZ110N08NS5	BT134-G
BSZ013NE2LS5I	BSZ068N06NS	BSZ120P03NS3 G	BT134W

Multisim 14.1 Education Components

BT136	BTA140	BUF_INV	BUK6507-55C
BT136-E	BTW38_600R	BUF601AP	BUK6507-75C
BT136-F	BTW40_400R	BUF602ID	BUK6510-75C
BT136-G	BTW42_600R	BUF602IDBVR	BUK652R1-30C
BT137	BTW43	BUF602IDG4	BUK652R6-40C
BT137-E	BTW45_400R	BUFFER	BUK653R3-30C
BT137-F	BTY79_400R	BUH100G	BUK653R4-40C
BT137-G	BTY91_400R	BUH150G	BUK653R5-55C
BT138	BU323ZG	BUH50G	BUK653R7-30C
BT138-E	BU406G	BUK6207-55C	BUK654R0-75C
BT138-F	BUB323ZG	BUK6209-30C	BUK654R6-55C
BT138-G	BUB323ZT4G	BUK6210-55C	BUK654R8-40C
BT139	BUCK_BOOST_CONVERTER	BUK6211-75C	BUK655R0-75C
BT139-E	BUCK_CONVERTER	BUK6212-40C	BUK6607-55C
BT139-F	BUCKCCM	BUK6213-30C	BUK6607-75C
BT139-G	BUCKCM	BUK6215-75C	BUK6610-75C
BT145_500R	BUCKDCM	BUK6217-55C	BUK661R8-30C
BT148_400R	BUCKVM	BUK6218-40C	BUK661R9-40C
BT148W_400R	BUD42D-1G	BUK6226-75C	BUK662R4-40C
BT149_B	BUD42DT4G	BUK6228-55C	BUK662R5-30C
BT150_500R	BUF	BUK6246-75C	BUK662R7-55C
BT151_500R	BUF_3S_AHOE	BUK624R5-30C	BUK663R2-40C
BT152_400R	BUF_3S_ALOE	BUK625R0-40C	BUK663R5-30C
BT153_500R	BUF_CO	BUK625R2-30C	BUK663R5-55C
BT169_B		BUK626R2-40C	BUK663R7-75C

Multisim 14.1 Education Components

BUK664R4-55C	BUK765R0-100E	BUK7Y12-40E	BUK7Y59-60E
BUK664R6-40C	BUK768R1-100E	BUK7Y12-55B	BUK7Y65-100E
BUK6C2R1-55C	BUK769R6-80E	BUK7Y13-40B	BUK7Y6R0-60E
BUK6C3R3-75C	BUK7E13-60E	BUK7Y14-80E	BUK7Y72-80E
BUK7514-60E	BUK7E1R6-30E	BUK7Y15-100E	BUK7Y7R6-40E
BUK751R6-30E	BUK7E1R8-40E	BUK7Y153-100E	BUK7Y7R8-80E
BUK751R8-40E	BUK7E1R9-40E	BUK7Y15-60E	BUK7Y8R7-60E
BUK752R3-40E	BUK7E2R3-40E	BUK7Y18-55B	BUK7Y98-80E
BUK752R7-60E	BUK7E2R6-60E	BUK7Y18-75B	BUK7Y9R9-80E
BUK753R1-40E	BUK7E3R1-40E	BUK7Y20-30B	BUK9515-60E
BUK753R5-60E	BUK7E3R5-60E	BUK7Y21-40E	BUK951R6-30E
BUK753R8-80E	BUK7E4R0-80E	BUK7Y22-100E	BUK951R9-40E
BUK754R0-40C	BUK7E4R6-60E	BUK7Y25-40B	BUK952R3-40E
BUK754R7-60E	BUK7E5R2-100E	BUK7Y25-60E	BUK952R8-60E
BUK755R4-100E	BUK7E8R3-40E	BUK7Y25-80E	BUK953R2-40E
BUK758R3-40E	BUK7K25-40E	BUK7Y28-75B	BUK953R5-60E
BUK7613-100E	BUK7K5R1-30E	BUK7Y29-40E	BUK954R4-80E
BUK761R3-30E	BUK7K5R6-30E	BUK7Y35-55B	BUK958R5-40E
BUK761R4-30E	BUK7K6R8-40E	BUK7Y38-100E	BUK9611-80E
BUK761R5-40E	BUK7Y07-30B	BUK7Y41-80E	BUK9615-100E
BUK761R6-40E	BUK7Y08-40B	BUK7Y43-60E	BUK961R4-30E
BUK762R4-60E	BUK7Y102-100B	BUK7Y4R4-40E	BUK961R5-30E
BUK7631-100E	BUK7Y10-30B	BUK7Y4R8-60E	BUK961R6-40E
BUK763R8-80E	BUK7Y113-100E	BUK7Y53-100B	BUK962R5-60E
BUK764R2-80E	BUK7Y12-100E	BUK7Y54-75B	BUK9637-100E

Multisim 14.1 Education Components

BUK964R2-80E	BUK9Y113-100E	BUK9Y4R4-40E	BUZ12
BUK964R7-80E	BUK9Y11-80E	BUK9Y4R8-60E	BUZ12AL
BUK965R8-100E	BUK9Y12-100E	BUK9Y53-100B	BUZ171
BUK969R3-100E	BUK9Y12-40E	BUK9Y58-75B	BUZ173
BUK9E15-60E	BUK9Y12-55B	BUK9Y59-60E	BUZ20
BUK9E1R6-30E	BUK9Y14-40B	BUK9Y65-100E	BUZ21
BUK9E2R3-40E	BUK9Y14-80E	BUK9Y6R0-60E	BUZ22
BUK9E2R8-60E	BUK9Y15-100E	BUK9Y72-80E	BUZ220
BUK9E3R7-60E	BUK9Y153-100E	BUK9Y7R6-40E	BUZ271
BUK9E4R4-80E	BUK9Y15-60E	BUK9Y8R5-80E	BUZ272
BUK9E4R9-60E	BUK9Y19-55B	BUK9Y8R7-60E	BUZ305
BUK9E6R1-100E	BUK9Y19-75B	BUL45D2G	BUZ30A
BUK9E8R5-40E	BUK9Y21-40E	BUL45G	BUZ31
BUK9K18-40E	BUK9Y22-100E	BUV21G	BUZ310
BUK9K29-100E	BUK9Y22-30B	BUV22G	BUZ311
BUK9K35-60E	BUK9Y25-60E	BUV26G	BUZ323
BUK9K45-100E	BUK9Y25-80E	BUX85G	BUZ325
BUK9K52-60E	BUK9Y27-40B	BUZ10	BUZ326
BUK9K6R2-40E	BUK9Y29-40E	BUZ100	BUZ331
BUK9K89-100E	BUK9Y30-75B	BUZ101	BUZ334
BUK9Y07-30B	BUK9Y38-100E	BUZ102	BUZ338
BUK9Y09-40B	BUK9Y3R0-40E	BUZ104	BUZ341
BUK9Y104-100B	BUK9Y40-55B	BUZ10L	BUZ342
BUK9Y107-80E	BUK9Y41-80E	BUZ10M	BUZ342KL
BUK9Y11-30B	BUK9Y43-60E	BUZ11GE	BUZ344

Multisim 14.1 Education Components

BUZ345	BUZ77A	BY713	BYD14K
BUZ346	BUZ78	BY714	BYD14M
BUZ350	BUZ80A	BY715	BYD17D
BUZ356	BUZ81	BY716	BYD17G
BUZ358	BUZ84A	BY717	BYD17J
BUZ40B	BUZ90	BY718	BYD17K
BUZ41A	BUZ91A	BY719	BYD17M
BUZ45B	BUZ92	BY720	BYD31D
BUZ50B	BUZZER	BY721	BYD31G
BUZ51	BVSS123LT1G	BY722	BYD31J
BUZ53A	BVSS138LT1G	BY723	BYD33D
BUZ60	BY228	BYD11	BYD33G
BUZ61A	BY328	BYD11D	BYD33J
BUZ64	BY438	BYD11G	BYD33K
BUZ70	BY448	BYD11J	BYD33M
BUZ71	BY458	BYD11K	BYD34D
BUZ71L	BY505	BYD11M	BYD34G
BUZ71LGE	BY527	BYD13D	BYD34J
BUZ72	BY584	BYD13G	BYD34K
BUZ72GE	BY627	BYD13J	BYD34M
BUZ73	BY705	BYD13K	BYD37D
BUZ73AGE	BY706	BYD13M	BYD37G
BUZ73L	BY710	BYD14D	BYD37J
BUZ74A	BY711	BYD14G	BYD37K
BUZ76	BY712	BYD14J	BYD37M

Multisim 14.1 Education Components

BYD73A	BYG22D-E3/TR	BYM36A	BYV28-200
BYD73B	BYG24J-E3/TR3	BYM36B	BYV28-50
BYD73C	BYM10-100	BYM36C	BYV32-200G
BYD73D	BYM10-1000	BYM36D	BYV36A
BYD73E	BYM10-1000-E3/97	BYM36E	BYV36B
BYD73F	BYM10-200	BYM56A	BYV36C
BYD73G	BYM10-400	BYM56B	BYV36D
BYD74A	BYM10-50	BYM56C	BYV36E
BYD74B	BYM10-600	BYM56D	BYV95A
BYD74C	BYM10-800	BYM56E	BYV95B
BYD74D	BYM11-100	BYS10-45-E3/TR	BYV95C
BYD74E	BYM11-1000	BYS11-90-E3/TR	BYV96D
BYD74F	BYM11-1000-E3/96	BYT28-300-E3/45	BYV96E
BYD74G	BYM11-100-E3/96	BYV10-20	BYW29-200G
BYD77A	BYM11-200	BYV10-30	BYW51-200G
BYD77B	BYM11-400	BYV10-40	BYW54
BYD77C	BYM11-50	BYV26A	BYW55
BYD77D	BYM11-600	BYV26B	BYW56
BYD77E	BYM11-800	BYV26C	BYW80-200G
BYD77F	BYM12-400-E3/96	BYV26D	BYW95A
BYD77G	BYM26A	BYV26E	BYW95B
BYG10G-E3/TR	BYM26B	BYV27-100	BYW95C
BYG10J-E3/TR	BYM26C	BYV27-50	BYW96D
BYG20J-E3/TR	BYM26D	BYV28-100	BYW96E
BYG21M-E3/TR	BYM26E	BYV28-150	BYX10G

Multisim 14.1 Education Components

BYX110GP	BZB784-C12	BZB84-B20	BZB84-B6V8
BZA408B	BZB784-C13	BZB84-B22	BZB84-B75
BZA418A	BZB784-C15	BZB84-B24	BZB84-B7V5
BZA420A	BZB784-C2V4	BZB84-B27	BZB84-B8V2
BZA456A	BZB784-C2V7	BZB84-B2V4	BZB84-B9V1
BZA462A	BZB784-C3V0	BZB84-B2V7	BZB84-C10
BZA820A	BZB784-C3V3	BZB84-B30	BZB84-C11
BZA856A	BZB784-C3V6	BZB84-B33	BZB84-C12
BZA856AL	BZB784-C3V9	BZB84-B36	BZB84-C13
BZA856AVL	BZB784-C4V3	BZB84-B39	BZB84-C15
BZA862A	BZB784-C4V7	BZB84-B3V0	BZB84-C16
BZA862AL	BZB784-C5V1	BZB84-B3V3	BZB84-C18
BZA862AVL	BZB784-C5V6	BZB84-B3V6	BZB84-C20
BZA868A	BZB784-C6V2	BZB84-B3V9	BZB84-C22
BZA868AL	BZB784-C6V8	BZB84-B43	BZB84-C24
BZA868AVL	BZB784-C7V5	BZB84-B47	BZB84-C27
BZA956A	BZB784-C8V2	BZB84-B4V3	BZB84-C2V4
BZA956AVL	BZB784-C9V1	BZB84-B4V7	BZB84-C2V7
BZA962A	BZB84-B10	BZB84-B51	BZB84-C30
BZA962AVL	BZB84-B11	BZB84-B56	BZB84-C33
BZA968A	BZB84-B12	BZB84-B5V1	BZB84-C36
BZA968AVL	BZB84-B13	BZB84-B5V6	BZB84-C39
BZB100A	BZB84-B15	BZB84-B62	BZB84-C3V0
BZB784-C10	BZB84-B16	BZB84-B68	BZB84-C3V3
BZB784-C11	BZB84-B18	BZB84-B6V2	BZB84-C3V6

Multisim 14.1 Education Components

BZB84-C3V9	BZB984-C3V3	BZT52H-B30	BZT52H-C18
BZB84-C43	BZB984-C3V6	BZT52H-B33	BZT52H-C20
BZB84-C47	BZB984-C3V9	BZT52H-B36	BZT52H-C22
BZB84-C4V3	BZB984-C4V3	BZT52H-B39	BZT52H-C24
BZB84-C4V7	BZB984-C4V7	BZT52H-B3V0	BZT52H-C27
BZB84-C51	BZB984-C5V1	BZT52H-B43	BZT52H-C2V4
BZB84-C56	BZB984-C5V6	BZT52H-B47	BZT52H-C2V7
BZB84-C5V1	BZB984-C6V2	BZT52H-B51	BZT52H-C30
BZB84-C5V6	BZB984-C6V8	BZT52H-B56	BZT52H-C33
BZB84-C62	BZB984-C7V5	BZT52H-B5V1	BZT52H-C36
BZB84-C68	BZB984-C8V2	BZT52H-B5V6	BZT52H-C39
BZB84-C6V2	BZB984-C9V1	BZT52H-B62	BZT52H-C3V0
BZB84-C6V8	BZT52H-B10	BZT52H-B68	BZT52H-C3V6
BZB84-C75	BZT52H-B11	BZT52H-B6V2	BZT52H-C3V9
BZB84-C7V5	BZT52H-B12	BZT52H-B6V8	BZT52H-C43
BZB84-C8V2	BZT52H-B13	BZT52H-B75	BZT52H-C47
BZB84-C9V1	BZT52H-B15	BZT52H-B7V5	BZT52H-C4V3
BZB984-C10	BZT52H-B16	BZT52H-B8V2	BZT52H-C4V7
BZB984-C11	BZT52H-B18	BZT52H-B9V1	BZT52H-C51
BZB984-C12	BZT52H-B20	BZT52H-C10	BZT52H-C56
BZB984-C13	BZT52H-B22	BZT52H-C11	BZT52H-C5V1
BZB984-C15	BZT52H-B24	BZT52H-C12	BZT52H-C5V6
BZB984-C2V4	BZT52H-B27	BZT52H-C13	BZT52H-C62
BZB984-C2V7	BZT52H-B2V4	BZT52H-C15	BZT52H-C68
BZB984-C3V0	BZT52H-B2V7	BZT52H-C16	BZT52H-C6V2

Multisim 14.1 Education Components

BZT52H-C6V8	BZV55-B3V0	BZV55-C18	BZV60-B15
BZT52H-C75	BZV55-B3V3	BZV55-C27	BZV60-B16
BZT52H-C7V5	BZV55-B3V6	BZV55-C2V4	BZV60-B18
BZT52H-C8V2	BZV55-B3V9	BZV55-C2V7	BZV60-B20
BZT52H-C9V1	BZV55-B43	BZV55-C33	BZV60-B22
BZV49-C12	BZV55-B47	BZV55-C3V0	BZV60-B24
BZV49-C16	BZV55-B4V3	BZV55-C3V3	BZV60-B27
BZV49-C3V6	BZV55-B4V7	BZV55-C3V6	BZV60-B2V4
BZV55-B10	BZV55-B51	BZV55-C3V9	BZV60-B2V7
BZV55-B11	BZV55-B56	BZV55-C43	BZV60-B30
BZV55-B12	BZV55-B5V1	BZV55-C47	BZV60-B33
BZV55-B13	BZV55-B5V6	BZV55-C4V3	BZV60-B36
BZV55-B15	BZV55-B68	BZV55-C4V7	BZV60-B39
BZV55-B16	BZV55-B6V2	BZV55-C5V1	BZV60-B3V0
BZV55-B18	BZV55-B6V8	BZV55-C5V6	BZV60-B3V3
BZV55-B20	BZV55-B75	BZV55-C6V2	BZV60-B3V6
BZV55-B22	BZV55-B7V5	BZV55-C6V8	BZV60-B3V9
BZV55-B24	BZV55-B8V2	BZV55-C7V5	BZV60-B43
BZV55-B27	BZV55-B9V1	BZV55-C8V2	BZV60-B47
BZV55-B2V4	BZV55-C10	BZV55-C9V1	BZV60-B4V3
BZV55-B2V7	BZV55-C11	BZV55-F2V4	BZV60-B4V7
BZV55-B30	BZV55-C12	BZV60-B10	BZV60-B51
BZV55-B33	BZV55-C13	BZV60-B11	BZV60-B56
BZV55-B36	BZV55-C15	BZV60-B12	BZV60-B5V1
BZV55-B39	BZV55-C16	BZV60-B13	BZV60-B5V6

Multisim 14.1 Education Components

BZV60-B62	BZV60-C3V0	BZV85-C15	BZV85-C7V5
BZV60-B68	BZV60-C3V3	BZV85-C16	BZV85-C8V2
BZV60-B6V2	BZV60-C3V6	BZV85-C18	BZV86-1V4
BZV60-B6V8	BZV60-C3V9	BZV85-C20	BZV86-2V0
BZV60-B75	BZV60-C43	BZV85-C22	BZV86-2V6
BZV60-B7V5	BZV60-C47	BZV85-C24	BZV86-3V2
BZV60-B8V2	BZV60-C4V3	BZV85-C27	BZV90-C10
BZV60-B9V1	BZV60-C4V7	BZV85-C30	BZV90-C11
BZV60-C10	BZV60-C51	BZV85-C33	BZV90-C12
BZV60-C11	BZV60-C56	BZV85-C36	BZV90-C13
BZV60-C12	BZV60-C5V1	BZV85-C39	BZV90-C15
BZV60-C13	BZV60-C5V6	BZV85-C3V6	BZV90-C16
BZV60-C15	BZV60-C62	BZV85-C3V9	BZV90-C18
BZV60-C16	BZV60-C68	BZV85-C43	BZV90-C20
BZV60-C18	BZV60-C6V2	BZV85-C47	BZV90-C22
BZV60-C20	BZV60-C6V8	BZV85-C4V3	BZV90-C24
BZV60-C22	BZV60-C75	BZV85-C4V7	BZV90-C27
BZV60-C24	BZV60-C7V5	BZV85-C51	BZV90-C2V4
BZV60-C27	BZV60-C8V2	BZV85-C5V1	BZV90-C2V7
BZV60-C2V4	BZV60-C9V1	BZV85-C5V6	BZV90-C30
BZV60-C2V7	BZV80	BZV85-C62	BZV90-C33
BZV60-C30	BZV85-C10	BZV85-C68	BZV90-C36
BZV60-C33	BZV85-C11	BZV85-C6V2	BZV90-C39
BZV60-C36	BZV85-C12	BZV85-C6V8	BZV90-C3V0
BZV60-C39	BZV85-C13	BZV85-C75	BZV90-C3V3

Multisim 14.1 Education Components

BZV90-C3V6	BZW03-C130	BZW03-C75	BZX384-B3V3
BZV90-C3V9	BZW03-C15	BZW03-C7V5	BZX384-B3V6
BZV90-C43	BZW03-C150	BZW03-C82	BZX384-B3V9
BZV90-C47	BZW03-C16	BZW03-C8V2	BZX384-B43
BZV90-C4V3	BZW03-C160	BZW03-C91	BZX384-B47
BZV90-C4V7	BZW03-C18	BZW03-C9V1	BZX384-B4V3
BZV90-C51	BZW03-C180	BZX100A	BZX384-B4V7
BZV90-C56	BZW03-C20	BZX384-B10	BZX384-B51
BZV90-C5V1	BZW03-C200	BZX384-B11	BZX384-B56
BZV90-C5V6	BZW03-C22	BZX384-B12	BZX384-B5V1
BZV90-C62	BZW03-C220	BZX384-B13	BZX384-B5V6
BZV90-C68	BZW03-C24	BZX384-B15	BZX384-B62
BZV90-C6V2	BZW03-C240	BZX384-B16	BZX384-B68
BZV90-C6V8	BZW03-C27	BZX384-B18	BZX384-B6V2
BZV90-C75	BZW03-C270	BZX384-B20	BZX384-B6V8
BZV90-C7V5	BZW03-C30	BZX384-B22	BZX384-B75
BZV90-C8V2	BZW03-C33	BZX384-B24	BZX384-B7V5
BZV90-C9V1	BZW03-C36	BZX384-B27	BZX384-B8V2
BZW03-C10	BZW03-C39	BZX384-B2V4	BZX384-B9V1
BZW03-C100	BZW03-C43	BZX384-B2V7	BZX384-C10
BZW03-C11	BZW03-C47	BZX384-B30	BZX384-C11
BZW03-C110	BZW03-C51	BZX384-B33	BZX384-C12
BZW03-C12	BZW03-C56	BZX384-B36	BZX384-C13
BZW03-C120	BZW03-C62	BZX384-B39	BZX384-C16
BZW03-C13	BZW03-C68	BZX384-B3V0	BZX384-C20

Multisim 14.1 Education Components

BZX384-C22	BZX384-C8V2	BZX55C4V3	BZX585-B24
BZX384-C24	BZX384-C9V1	BZX55C4V7	BZX585-B27
BZX384-C2V4	BZX55C10	BZX55C51	BZX585-B2V4
BZX384-C2V7	BZX55C11	BZX55C56	BZX585-B2V7
BZX384-C30	BZX55C12	BZX55C5V1	BZX585-B30
BZX384-C33	BZX55C13	BZX55C5V6	BZX585-B33
BZX384-C36	BZX55C15	BZX55C62	BZX585-B36
BZX384-C39	BZX55C16	BZX55C68	BZX585-B39
BZX384-C3V0	BZX55C18	BZX55C6V2	BZX585-B3V0
BZX384-C3V3	BZX55C20	BZX55C6V8	BZX585-B3V3
BZX384-C3V6	BZX55C22	BZX55C75	BZX585-B3V6
BZX384-C3V9	BZX55C24	BZX55C7V5	BZX585-B3V9
BZX384-C43	BZX55C27	BZX55C82	BZX585-B43
BZX384-C47	BZX55C2V4	BZX55C8V2	BZX585-B47
BZX384-C4V3	BZX55C2V7	BZX55C91	BZX585-B4V3
BZX384-C4V7	BZX55C30	BZX55C9V1	BZX585-B4V7
BZX384-C51	BZX55C33	BZX585-B10	BZX585-B51
BZX384-C56	BZX55C36	BZX585-B11	BZX585-B56
BZX384-C5V1	BZX55C39	BZX585-B12	BZX585-B5V1
BZX384-C62	BZX55C3V0	BZX585-B13	BZX585-B5V6
BZX384-C68	BZX55C3V3	BZX585-B15	BZX585-B62
BZX384-C6V2	BZX55C3V6	BZX585-B16	BZX585-B68
BZX384-C6V8	BZX55C3V9	BZX585-B18	BZX585-B6V2
BZX384-C75	BZX55C43	BZX585-B20	BZX585-B6V8
BZX384-C7V5	BZX55C47	BZX585-B22	BZX585-B75

Multisim 14.1 Education Components

BZX585-B7V5	BZX585-C51	BZX79-A33	BZX79-B12
BZX585-B8V2	BZX585-C56	BZX79-A36	BZX79-B13
BZX585-B9V1	BZX585-C5V1	BZX79-A3V0	BZX79-B15
BZX585-C10	BZX585-C62	BZX79-A3V3	BZX79-B16
BZX585-C11	BZX585-C68	BZX79-A3V6	BZX79-B18
BZX585-C12	BZX585-C6V2	BZX79-A3V9	BZX79-B20
BZX585-C13	BZX585-C6V8	BZX79-A40	BZX79-B22
BZX585-C16	BZX585-C75	BZX79-A43	BZX79-B24
BZX585-C20	BZX585-C7V5	BZX79-A47	BZX79-B27
BZX585-C22	BZX585-C8V2	BZX79-A4V3	BZX79-B2V4
BZX585-C24	BZX585-C9V1	BZX79-A4V7	BZX79-B2V7
BZX585-C2V4	BZX79-A10	BZX79-A51	BZX79-B30
BZX585-C2V7	BZX79-A11	BZX79-A56	BZX79-B33
BZX585-C30	BZX79-A12	BZX79-A5V1	BZX79-B36
BZX585-C33	BZX79-A13	BZX79-A5V6	BZX79-B39
BZX585-C36	BZX79-A15	BZX79-A62	BZX79-B3V3
BZX585-C39	BZX79-A16	BZX79-A68	BZX79-B3V6
BZX585-C3V0	BZX79-A18	BZX79-A6V2	BZX79-B3V9
BZX585-C3V3	BZX79-A20	BZX79-A6V8	BZX79-B43
BZX585-C3V6	BZX79-A22	BZX79-A75	BZX79-B47
BZX585-C3V9	BZX79-A24	BZX79-A7V5	BZX79-B4V3
BZX585-C43	BZX79-A27	BZX79-A8V2	BZX79-B4V7
BZX585-C47	BZX79-A2V4	BZX79-A9V1	BZX79-B51
BZX585-C4V3	BZX79-A2V7	BZX79-B10	BZX79-B56
BZX585-C4V7	BZX79-A30	BZX79-B11	BZX79-B5V1

Multisim 14.1 Education Components

BZX79-B62	BZX79-C24	BZX79-C7V5	BZX83-C5V1
BZX79-B68	BZX79-C27	BZX79-C82	BZX83-C5V6
BZX79-B6V2	BZX79-C2V4	BZX79-C8V2	BZX83-C6V2
BZX79-B6V8	BZX79-C2V7	BZX79-C91	BZX83-C6V8
BZX79-B75	BZX79-C30	BZX79-C9V1	BZX83-C7V5
BZX79-B7V5	BZX79-C33	BZX83-C10	BZX83-C8V2
BZX79-B8V2	BZX79-C36	BZX83-C11	BZX83-C9V1
BZX79-B9V1	BZX79-C39	BZX83-C12	BZX84-A10
BZX79-C10	BZX79-C3V0	BZX83-C13	BZX84-A11
BZX79-C100	BZX79-C3V3	BZX83-C15	BZX84-A12
BZX79-C11	BZX79-C3V6	BZX83-C16	BZX84-A13
BZX79-C110	BZX79-C3V9	BZX83-C18	BZX84-A15
BZX79-C12	BZX79-C43	BZX83-C20	BZX84-A16
BZX79-C120	BZX79-C47	BZX83-C22	BZX84-A18
BZX79-C13	BZX79-C4V3	BZX83-C24	BZX84-A20
BZX79-C130	BZX79-C4V7	BZX83-C27	BZX84-A22
BZX79-C15	BZX79-C51	BZX83-C2V7	BZX84-A24
BZX79-C150	BZX79-C56	BZX83-C30	BZX84-A27
BZX79-C16	BZX79-C5V1	BZX83-C33	BZX84-A2V4
BZX79-C160	BZX79-C5V6	BZX83-C3V0	BZX84-A2V7
BZX79-C18	BZX79-C62	BZX83-C3V3	BZX84-A30
BZX79-C180	BZX79-C68	BZX83-C3V6	BZX84-A33
BZX79-C20	BZX79-C6V2	BZX83-C3V9	BZX84-A36
BZX79-C200	BZX79-C6V8	BZX83-C4V3	BZX84-A39
BZX79-C22	BZX79-C75	BZX83-C4V7	BZX84-A3V0

Multisim 14.1 Education Components

BZX84-A3V3	BZX84B16LT1G	BZX84-B5V6	BZX84-C18
BZX84-A3V6	BZX84-B18	BZX84B5V6LT1G	BZX84-C20
BZX84-A3V9	BZX84-B20	BZX84-B62	BZX84-C22
BZX84-A43	BZX84-B22	BZX84-B68	BZX84-C24
BZX84-A47	BZX84-B24	BZX84-B6V2	BZX84-C27
BZX84-A4V3	BZX84-B27	BZX84B6V2LT1G	BZX84-C2V4
BZX84-A4V7	BZX84-B2V4	BZX84-B6V8	BZX84-C2V7
BZX84-A51	BZX84-B2V7	BZX84B6V8LT1G	BZX84-C30
BZX84-A56	BZX84-B30	BZX84-B75	BZX84-C33
BZX84-A5V1	BZX84-B33	BZX84-B7V5	BZX84C33LT1G
BZX84-A5V6	BZX84-B36	BZX84B7V5LT1G	BZX84C33LT3G
BZX84-A62	BZX84-B39	BZX84-B8V2	BZX84-C36
BZX84-A68	BZX84-B3V0	BZX84B8V2LT1G	BZX84C36LT1G
BZX84-A6V2	BZX84-B3V3	BZX84-B9V1	BZX84-C39
BZX84-A6V8	BZX84-B3V6	BZX84B9V1LT1G	BZX84-C3V0
BZX84-A75	BZX84-B3V9	BZX84-C10	BZX84C3V0LT1G
BZX84-A7V5	BZX84-B43	BZX84-C11	BZX84-C3V3
BZX84-A8V2	BZX84-B47	BZX84-C12	BZX84-C3V6
BZX84-A9V1	BZX84-B4V3	BZX84C12LT1G	BZX84-C3V9
BZX84-B10	BZX84-B4V7	BZX84-C13	BZX84-C43
BZX84-B11	BZX84B4V7LT1G	BZX84-C15	BZX84-C47
BZX84-B12	BZX84-B51	BZX84C15LT1	BZX84-C4V3
BZX84-B13	BZX84-B56	BZX84C15LT1G	BZX84-C4V7
BZX84-B15	BZX84-B5V1	BZX84C15LT3G	BZX84C4V7LT1G
BZX84-B16	BZX84B5V1LT1G	BZX84-C16	BZX84C4V7LT3G

Multisim 14.1 Education Components

BZX84-C51	BZX84C9V1LT3G	BZX84J-B4V7	BZX84J-C2V7
BZX84-C56	BZX84J-B10	BZX84J-B51	BZX84J-C30
BZX84-C5V1	BZX84J-B11	BZX84J-B56	BZX84J-C33
BZX84C5V1LT1G	BZX84J-B12	BZX84J-B5V1	BZX84J-C36
BZX84C5V1LT3G	BZX84J-B13	BZX84J-B5V6	BZX84J-C39
BZX84-C5V6	BZX84J-B15	BZX84J-B62	BZX84J-C3V0
BZX84C5V6LT1G	BZX84J-B16	BZX84J-B68	BZX84J-C3V3
BZX84C5V6LT3G	BZX84J-B18	BZX84J-B6V2	BZX84J-C3V6
BZX84-C62	BZX84J-B20	BZX84J-B6V8	BZX84J-C3V9
BZX84-C68	BZX84J-B22	BZX84J-B75	BZX84J-C43
BZX84C68LT1G	BZX84J-B24	BZX84J-B7V5	BZX84J-C47
BZX84-C6V2	BZX84J-B27	BZX84J-B8V2	BZX84J-C4V3
BZX84C6V2LT1G	BZX84J-B2V4	BZX84J-B9V1	BZX84J-C4V7
BZX84C6V2LT3G	BZX84J-B2V7	BZX84J-C10	BZX84J-C51
BZX84-C6V8	BZX84J-B30	BZX84J-C11	BZX84J-C56
BZX84C6V8LT1G	BZX84J-B33	BZX84J-C12	BZX84J-C5V1
BZX84C6V8LT3G	BZX84J-B36	BZX84J-C13	BZX84J-C5V6
BZX84-C75	BZX84J-B39	BZX84J-C15	BZX84J-C62
BZX84C75LT1G	BZX84J-B3V0	BZX84J-C16	BZX84J-C68
BZX84-C7V5	BZX84J-B3V3	BZX84J-C18	BZX84J-C6V2
BZX84C7V5LT1G	BZX84J-B3V6	BZX84J-C20	BZX84J-C6V8
BZX84-C8V2	BZX84J-B3V9	BZX84J-C22	BZX84J-C75
BZX84C8V2LT1G	BZX84J-B43	BZX84J-C24	BZX84J-C7V5
BZX84-C9V1	BZX84J-B47	BZX84J-C27	BZX84J-C8V2
BZX84C9V1LT1G	BZX84J-B4V3	BZX84J-C2V4	BZX84J-C9V1

Multisim 14.1 Education Components

BZX85-C10	BZX85-C5V1	BZX884-B30	BZX884-C11
BZX85-C100	BZX85-C5V6	BZX884-B33	BZX884-C12
BZX85-C11	BZX85-C62	BZX884-B36	BZX884-C13
BZX85-C12	BZX85-C68	BZX884-B39	BZX884-C16
BZX85-C13	BZX85-C6V2	BZX884-B3V0	BZX884-C20
BZX85-C15	BZX85-C6V8	BZX884-B3V3	BZX884-C22
BZX85-C16	BZX85-C75	BZX884-B3V6	BZX884-C24
BZX85-C18	BZX85-C7V5	BZX884-B3V9	BZX884-C2V4
BZX85-C20	BZX85-C82	BZX884-B43	BZX884-C2V7
BZX85-C22	BZX85-C8V2	BZX884-B47	BZX884-C30
BZX85-C24	BZX85-C91	BZX884-B4V3	BZX884-C33
BZX85-C27	BZX85-C9V1	BZX884-B4V7	BZX884-C36
BZX85-C30	BZX884-B10	BZX884-B51	BZX884-C3V0
BZX85-C33	BZX884-B11	BZX884-B56	BZX884-C3V3
BZX85-C36	BZX884-B12	BZX884-B5V1	BZX884-C3V6
BZX85-C39	BZX884-B13	BZX884-B5V6	BZX884-C3V9
BZX85-C3V3	BZX884-B15	BZX884-B62	BZX884-C43
BZX85-C3V6	BZX884-B16	BZX884-B68	BZX884-C47
BZX85-C3V9	BZX884-B18	BZX884-B6V2	BZX884-C4V3
BZX85-C43	BZX884-B20	BZX884-B6V8	BZX884-C4V7
BZX85-C47	BZX884-B22	BZX884-B75	BZX884-C51
BZX85-C4V3	BZX884-B24	BZX884-B7V5	BZX884-C56
BZX85-C4V7	BZX884-B27	BZX884-B8V2	BZX884-C5V1
BZX85-C51	BZX884-B2V4	BZX884-B9V1	BZX884-C62
BZX85-C56	BZX884-B2V7	BZX884-C10	BZX884-C68

Multisim 14.1 Education Components

BZX884-C6V2	CA0258AM	CA3078E	CA3140M
BZX884-C75	CA0258AT	CA3078M	CA3140T
BZX884-C7V5	CA0258E	CA3078T	CA3160E
BZX884-C8V2	CA0258M	CA3080	CA3160T
BZX884-C9V1	CA0258T	CA3080A	CA3193AE
C232A	CA0324E	CA3080AE	CA3193AT
C232B	CA0324M	CA3080AM	CA3193E
C232D	CA0358AE	CA3080E	CA3193T
C232F	CA0358AM	CA3080M	CA3240AE
C232M	CA0358AT	CA3094AE	CA3240AE1
C233A	CA0358E	CA3094AM	CA3240E
C233B	CA0358M	CA3094AT	CA3240E1
C233D	CA0358T	CA3094BE	CA3260E
C233F	CA0741E	CA3094BM	CA3260T
C233M	CA0741T	CA3094BT	CA3280E
CA0124E	CA1458E	CA3094E	CA3440AE
CA0124M	CA1458T	CA3094M	CA3440M
CA0158AE	CA2902M	CA3094T	CA3450E
CA0158AT	CA2902N	CA3100E	CA5130AE
CA0158E	CA2904E	CA3100M	CA5130AM
CA0158M	CA2904M	CA3100T	CA5130AT
CA0158T	CA3060E	CA3130E	CA5130E
CA0224E	CA3078AE	CA3130M	CA5130M
CA0224M	CA3078AM	CA3130T	CA5130T
CA0258AE	CA3078AT	CA3140E	CA5160AE

Multisim 14.1 Education Components

CA5160AM	CHIRP_VOLTAGE	CLC402A8D	CLC409AJP
CA5260AE	CLC103AI	CLC402AID	CLC410A8B
CA5260AM	CLC103AM	CLC402AJE	CLC410A8D
CA5260E	CLC111AJE	CLC402AJP	CLC410AJE
CA5260M	CLC111AJP	CLC404A8D	CLC410AJP
CA5420E	CLC200A8C	CLC404AID	CLC411A8B
CA5420M	CLC200AI	CLC404AJE	CLC411AJE
CA5420T	CLC200AK	CLC404AJM5	CLC411AJP
CA5470E	CLC200AM	CLC404AJP	CLC412A8B
CA5470M	CLC201	CLC405A8B	CLC412AIB
CAP_ELECTROLIT_VIRTUAL	CLC203	CLC405AIB	CLC412AJE
	CLC220	CLC405AJE	CLC412AJP
CAPACITOR_POL_RATED	CLC400A8B	CLC405AJP	CLC414A8B
CAPACITOR_RATED	CLC400A8D	CLC406A8B	CLC414A8D
CAPACITOR_VIRTUAL	CLC400AIB	CLC406A8D	CLC414AJE
	CLC400AID	CLC406AJE	CLC414AJP
Capacitor1_100uF	CLC400AJE	CLC406AJM5	CLC415A8B
Capacitor2_10pF	CLC400AJP	CLC406AJP	CLC415A8D
Capacitor3_100pF	CLC401A8B	CLC407AIB	CLC415AJE
CCM-DCM1	CLC401A8D	CLC407AJE	CLC415AJP
CCM-DCM2	CLC401AIB	CLC407AJP	CLC416AJE
CD4538BCM	CLC401AID	CLC409A8D	CLC416AJP
CD4538BCN	CLC401AJE	CLC409AID	CLC417AJE
CD4538BCWM	CLC401AJP	CLC409AJE	CLC417AJP
CHIRP_CURRENT	CLC402A8B	CLC409AJM5	CLC420A8B

Multisim 14.1 Education Components

CLC420A8D	CLC431A8B	CM1213A-02SR	CNY17F-3X016
CLC420AIB	CLC431AJE	CM1624-08DE	CNY17F-3X017
CLC420AJE	CLC431AJP	CNTR_16SBIN	CNY17F-3X019
CLC420AJP	CLC432A8B	CNTR_4ABIN	COMP_4
CLC420B8B	CLC432AJE	CNTR_4ADEC	COMPARATOR_IDE AL
CLC420B8D	CLC432AJP	CNTR_4BIN_AS	COMPARATOR_VIR TUAL
CLC420BIB	CLC440A8B	CNTR_4BIN_ASCLR	COMPARHYS
CLC420BJE	CLC440AJE	CNTR_4BIN_S	CONTROL_1A
CLC420BJP	CLC440AJP	CNTR_4BIN_SU_D	CONTROL_1C
CLC423AJE	CLC449A8B	CNTR_4BINS_DC	CONTROL_2A
CLC423AJP	CLC449AJE	CNTR_4SBIN	CONTROL_2C
CLC425A8B	CLC449AJP	CNTR_4SDEC	CONTROL_3A
CLC425AIB	CLC501A8D	CNTR_7BIN	CONTROL_3C
CLC425AJE	CLC501AID	CNTR_8SBIN	CONTROL_4A
CLC425AJP	CLC501AJE	CNTR_BCD_S	CONTROL_4C
CLC426A8B	CLC501AJP	CNTR_BCD_SDC	CONTROL_NC
CLC426AIB	CLC502A8D	CNTR_BCD_SU_D	CONTROL_NO
CLC426AJE	CLC502AID	CNTR_BIN_DEC_SU _D	CONTROLLED_ONE _SHOT
CLC426AJP	CLC502AJE	CNTR_JOHNSON	CONVEYOR_BELT
CLC428A8B	CLC502AJP	CNY17F-3	CORELESS_COIL_VI RTUAL
CLC428AJE	CLC505A8D	CNY17F-3X001	CORESAT
CLC428AJP	CLC505AJE	CNY17F-3X006	COUNT_OFF
CLC430A8B	CLC505AJP	CNY17F-3X007T	
CLC430AJE	CLOCK_CURRENT	CNY17F-3X009T	
CLC430AJP	CLOCK_VOLTAGE		

Multisim 14.1 Education Components

COUNT_OFF	CPH3205-TL-E	CPH6443-TL-H	D44C12G
COUNT_OFF_HOLD	CPH3223-TL-E	CPH6443-TL-W	D44H11G
COUNT_OFF_HOLD	CPH3348-TL-E	CPH6444-TL-W	D44H8G
COUNT_OFF_RESET	CPH3348-TL-W	CPH6445-TL-E	D44VH10G
COUNT_OFF_RESET	CPH3362-TL-W	CPH6531-TL-E	D45C12G
COUNT_OFF_UPD WN	CPH3448-TL-H	CPM	D45H11G
COUNT_ON	CPH3456-TL-H	CRYSTAL_VIRTUAL	D45H8G
COUNT_ON	CPH3456-TL-W	CURRENT_CONTRO LLED_CURRENT_SO URCE	D45VH10G
COUNT_ON_HOLD	CPH3457-TL-H		DAC7642_FP32
COUNT_ON_HOLD	CPH3457-TL-W	CURRENT_CONTRO LLED_SPST	DAC7643_FP32
COUNT_ON_HOLD	CPH3461-TL-H		DAC8541
COUNT_ON_RESET	CPH3461-TL-W	CURRENT_CONTRO LLED_SPST_ANIMA TED	DAN222M3T5G
COUNT_ON_RESET	CPH3910-TL-E		DAP222M3T5G
COUNT_ON_UPDW N	CPH5505-TL-E	CURRENT_CONTRO LLED_VOLTAGE_SO URCE	DBREAK
COUNT_UPDOWN_O FF	CPH5506-TL-E		DC_CURRENT
COUNT_UPDOWN_O N	CPH5617-TL-E	CURRENT_LIMITER_ BLOCK	DC_INTERACTIVE_C URRENT
Counter_74LS160N	CPH5871-TL-H		DC_INTERACTIVE_V OLTAGE
COUPLED_INDUCT ORS	CPH5871-TL-W	CYPRESS-ULTRA- ISR-HDR	
	CPH5905G-TL-E		DC_MACHINE_PER MANENT_MAGNET
CPH3105-TL-E	CPH6223-TL-E	D_FF	
CPH3122-TL-E	CPH6337-TL-E	D_FF_NEGSR	DC_MACHINE_WO UND_FIELD
CPH3123-TL-E	CPH6337-TL-W	D_FF_POSSR	
CPH3144-TL-E	CPH6341-TL-E	D_LATCH	DC_POWER
CPH3145-TL-E	CPH6347-TL-H	D_LATCH_NEGSR	DC_XFMR
	CPH6347-TL-W	D1N4148	DCC010-TB-E

Multisim 14.1 Education Components

DCD_2TO4	DEM4_16	DIP12	DPST_2NC_DB
DCD_3TO8	DF06MA-E3/45	DIP14	DPST_2NC_SB
DCD_4TO16	DF10S/45	DIP16	DPST_2NO_DB
DCD_7SEG	DF10SA-E3/45	DIP18	DPST_2NO_SB
DCD_7SEG_P	DF1510S-E3/77	DIP20	DQ_TO_ABC
DCD_BARGRAPH	DF3A6.8FUT1G	DIP22	DRV103H
DCD_HEX	DF6A6.8FUT1G	DIP24	DRV103U
DCD_HEX_BLUE	DGND	DIP28	DRV104PWP
DCD_HEX_DIG_BLUE	DIGITAL_CLOCK	DIP4	DRV632PW
DCD_HEX_DIG_GREEN	DIGITAL_CONSTANT	DIP6	DRV8832DGQ
DCD_HEX_DIG_ORANGE	DIGITAL_FREQUENCY_DIVIDER	DIP8	DRV8832DRCR
DCD_HEX_DIG_RED	DIGITAL_HIGH	DIPSW1	DRV8837DSGT
DCD_HEX_DIG_YELLOW	DIGITAL_LOW	DIPSW10	DSL70
DCD_HEX_GREEN	DIGITAL_PULLDOWN	DIPSW2	DSUB15F
DCD_HEX_ORANGE	DIGITAL_PULLUP	DIPSW3	DSUB15F-VGA
DCD_HEX_YELLOW	DIGITAL_STATE_MACHINE	DIPSW4	DSUB15M
DEC_BCD_10_INV	DIODE	DIPSW5	DSUB15M-VGA
DEC_BCD_7	DIODE	DIPSW6	DSUB25F
DEC2_4	DIODE_RATED	DIPSW7	DSUB25M
DEC3_8	DIODE_THERMAL	DIPSW8	DSUB37F
DEC4_10	Diode1	DIPSW9	DSUB37M
DELAY	DIP10	DIV	DSUB9F
		DIVIDER	DSUB9M
		DPDT_DB	DSWPK_10
		DPDT_SB	DSWPK_2

Multisim 14.1 Education Components

DSWPK_3	DTA143EET1G	DTC123TM3T5G	ECH8649-TL-H
DSWPK_4	DTA143EM3T5G	DTC124EET1G	ECH8651R-R-TL-H
DSWPK_5	DTA143ZET1G	DTC124EM3T5G	ECH8651R-TL-H
DSWPK_6	DTA143ZM3T5G	DTC124XET1G	ECH8652-TL-H
DSWPK_7	DTA144EET1G	DTC124XM3T5G	ECH8653-TL-H
DSWPK_8	DTA144EM3T5G	DTC143EET1G	ECH8654-TL-H
DSWPK_9	DTA144TET1G	DTC143EM3T5G	ECH8655R-TL-H
DTA113EET1G	DTA144TM3T5G	DTC143TM3T5G	ECH8657-TL-H
DTA113EM3T5G	DTA144WM3T5G	DTC143ZET1G	ECH8659-TL-H
DTA114EET1G	DTAND	DTC143ZM3T5G	ECH8659-TL-W
DTA114EM3T5G	DTC113EET1G	DTC144EET1G	ECH8660-TL-H
DTA114TET1G	DTC113EM3T5G	DTC144EM3T5G	ECH8661-TL-H
DTA114TM3T5G	DTC114EET1G	DTC144TET1G	ECH8662-TL-H
DTA114YET1G	DTC114EM3T5G	DTC144TM3T5G	ECH8667-TL-H
DTA114YM3T5G	DTC114TET1G	DTC144WM3T5G	ECH8690-TL-H
DTA115EET1G	DTC114TM3T5G	DTMF_KEYPAD	ECH8693R-TL-W
DTA115EM3T5G	DTC114YET1G	ECG6407	ECH8697R-TL-W
DTA115TET1G	DTC115EET1G	ECG6408	EDF1DS-E3/45
DTA115TM3T5G	DTC115EM3T5G	ECG6411	EDR201A05
DTA123EM3T5G	DTC115TET1G	ECG6412	EDR201A12
DTA123TET1G	DTC115TM3T5G	ECH8102-TL-H	EDR201A24
DTA123TM3T5G	DTC123EM3T5G	ECH8310-TL-H	EDR2H1A05
DTA124EET1G	DTC123JET1G	ECH8315-TL-H	EDR2H1A12
DTA124EM3T5G	DTC123JM3T5G	ECH8315-TL-W	EDR2H1A24
DTA124XM3T5G	DTC123TET1G	ECH8420-TL-H	EGF1D-E3/67A

Multisim 14.1 Education Components

EGF1T-E3/67A	EL2500/EL	Elvis_Left_Rail3	EMR011A09
EGP10D-E3/54	EL2520/EL	Elvis_Left_Rail4	EMR011A12
EGP10G-E3/54	EL2600/EL	Elvis_Left_Rail5	EMR011A24
EGP50D-E3/54	EL2620/EL	Elvis_Left_Rail6	EMR011B03
EGP50G-E3/54	EL4089CN	Elvis_Left_Rail7	EMR011B05
EL2006CG	EL4089CS	Elvis_Left_Rail8	EMR011B06
EL2006G	EL4430CN	Elvis_Left_Rail9	EMR011B08
EL2006G/883B	EL4430CS	Elvis_Right_Rail	EMR011B09
EL2022/EL	EL4451CN	ElvisLbIA	EMR011B12
EL2022CG	EL4451CS	ElvisLbIB	EMR011B24
EL2022G	EL4452CN	ElvisResistor	EMR021A03
EL2157CN	EL4452CS	EMC2DXV5T1G	EMR021A05
EL2157CS	ELH0032G/883B	EMC3DXV5T1G	EMR021A06
EL2210CN	ELH0101K/883B	EMC3DXV5T5G	EMR021A08
EL2210CS	Elvis_II_Rail_left_Bottom	EMC4DXV5T1G	EMR021A09
EL2211CN	Elvis_II_Rail_Left_Top	EMC5DXV5T1G	EMR021A12
EL2211CS		EMH1303-TL-E	EMR021A24
EL2310CN	Elvis_II_Rail_Right_Bottom	EMH1307-TL-H	EMR021B03
EL2310CS		EMH1405-TL-H	EMR021B05
EL2311CN	Elvis_II_Rail_Right_Top	EMH2407-TL-H	EMR021B06
EL2311CS	Elvis_II_top_fixed_1	EMH2408-TL-H	EMR021B08
EL2410CN	Elvis_II_top_fixed_2	EMR011A03	EMR021B09
EL2410CS	Elvis_Left_Rail1	EMR011A05	EMR021B12
EL2411CN	Elvis_Left_Rail2	EMR011A06	EMR021B24
EL2411CS		EMR011A08	EMR031A03

Multisim 14.1 Education Components

EMR031A05	EMR121B12	EMR161A06	EP2015CM
EMR031A06	EMR121B24	EMR161A08	EP2015CN
EMR031A08	EMR131A03	EMR161A09	EPC2001
EMR031A09	EMR131A05	EMR161A12	EPC2001C
EMR031A12	EMR131A06	EMR171A03	EPC2007
EMR031A24	EMR131A08	EMR171A05	EPC2007C
EMR031B03	EMR131A09	EMR171A06	EPC2010
EMR031B05	EMR131A12	EMR171A08	EPC2010C
EMR031B06	EMR131A24	EMR171A09	EPC2012
EMR031B08	EMR131B03	EMR171A12	EPC2012C
EMR031B09	EMR131B05	EMR171A24	EPC2014
EMR031B12	EMR131B06	EMX1DXV6T1G	EPC2014C
EMR031B24	EMR131B08	EMX1DXV6T5G	EPC2015
EMR121A03	EMR131B09	EN2016CM	EPC2015C
EMR121A05	EMR131B12	EN2016CN	EPC2016
EMR121A06	EMR131B24	ENC_10TO4	EPC2016C
EMR121A08	EMR151A03	ENC_8TO3	EPC2018
EMR121A09	EMR151A05	ENC_8TO3S	EPC2019
EMR121A12	EMR151A06	ENC10_4	EPC2020
EMR121A24	EMR151A08	ENC8_3	EPC2021
EMR121B03	EMR151A09	ENERGIZING_COIL	EPC2022
EMR121B05	EMR151A12	ENERGIZING_COIL_ AC	EPC2023
EMR121B06	EMR151A24	ENERGIZING_COIL_ TIMED	EPC2024
EMR121B08	EMR161A03		EPC2025
EMR121B09	EMR161A05	EP2015ACN	EPC2029

Multisim 14.1 Education Components

EPC2030	EPC8005	ESD108-B1-CSP0201	ESD207-B1-02EL
EPC2031	EPC8007	ESD110-B1-02EL	ESD207-B1-02ELS
EPC2032	EPC8008	ESD110-B1-02ELS	ESD208-B1-02EL
EPC2033	EPC8009	ESD112-B1-02EL	ESD208-B1-02ELS
EPC2034	EPC8010	ESD112-B1-02ELS	ESD217-B1-02EL
EPC2035	ERRAMP	ESD113-B1-02EL	ESD218-B1-02ELS
EPC2036	ES1B-E3/61T	ESD113-B1-02ELS	ESD221-U1-02EL
EPC2038	ES1C-E3/61T	ESD119-B1-W01005	ESD24VS2U
EPC2039	ES1D-E3/61T	ESD11L5.0DT5G	ESD300-B1-02LRH
EPC2100	ES1PD-E3/84A	ESD129-B1-W01005	ESD307-U1-02N
EPC2101	ES2B-E3/52T	ESD18VU1B-02LRH	ESD311-U1-02N
EPC2102	ES2C-E3/52T	ESD18VU1B-02LS	ESD3V3U4ULC
EPC2103	ES2D-E3/52T	ESD200-B1-CSP0201	ESD5004MXTBG
EPC2104	ES3D-E3/57T	ESD202-B1-CSP01005	ESD5371MXT5G
EPC2105	ESD0P2RF-02LRH	ESD203-B1-02EL	ESD5581MXT5G
EPC2106	ESD0P2RF-02LS	ESD203-B1-02ELS	ESD5B5.0ST1G
EPC2107	ESD101-B1-02EL	ESD204-B1-02EL	ESD5V3L1B-02LS
EPC2108	ESD101-B1-02ELS	ESD204-B1-02ELS	ESD5V3L1U-02LRH
EPC2110	ESD102-U1-02ELS	ESD205-B1-02EL	ESD5V3U2U-03F
EPC2801	ESD102-U2-099EL	ESD205-B1-02ELS	ESD5V3U2U-03LRH
EPC2815	ESD102-U4-05L	ESD206-B1-02EL	ESD5V3U4RRS
EPC2818	ESD103-B1-02EL	ESD206-B1-02ELS	ESD5V3U4U-HDMI
EPC8002	ESD103-B1-02ELS	ESD206-B1-02V	ESD5V5U5ULC
EPC8003	ESD105-B1-02EL		ESD5Z12T1G
EPC8004	ESD105-B1-02ELS		ESD5Z2.5T1G

Multisim 14.1 Education Components

ESD5Z3.3T1G	ESD9X3.3ST5G	F1240	FES16GT-E3/45
ESD5Z5.0T1G	ESD9X5.0ST5G	F1260	FES8DT-E3/45
ESD5Z6.0T1G	ESDR0502NMUTAG	F2001	FF_D_CO
ESD5Z7.0T1G	ESDR0502NMUTBG	F2002	FF_D_PCLR_CO
ESD5Z7.0T5G	ESDR0544MDMR4G	F2012	FF_D4_CLR_CO
ESD7004MUTAG	ESH1PD-E3/84A	F2021	FF_JK_NSCLR_CO
ESD7008MUTAG	EVAL-SDP-CB1Z	F2046	FF_JK_PSCLR_CO
ESD7016MUTAG	EVAL-SDP-CH1Z	F2047	FF_T_CLR_CO
ESD7104MUTAG	EVAL-SDP-CH1Z_FMC	F2048	FF200R12KE4
ESD7181MUT5G	EVAL-SDP-CS1Z	F2201S	FF300R12KE4
ESD7462N2T5G	EXPONENTIAL_CURRENT	F2202S	FF450R12KE4
ESD7951ST5G	EXPONENTIAL_VOLTAGE	FAST_1A	FLOAT_NC
ESD7C3.3DT5G		FAST_2A	FLOAT_NO
ESD7C5.0DT5G		FAST_3A	FLOW_NC
ESD8004MUTAG	F1007	FAST_4A	FLOW_NO
ESD8011MUT5G	F1008	FCN-268D024-G/10-R	FLYBACKCCM
ESD8040MUTAG	F1020	FCX458	FLYBACKCM
ESD8V0R1B-02EL	F1021	FCX558	FLYBACKDCM
ESD8V0R1B-02ELS	F1022	FCX649	FLYBACKVM
ESD9B3.3ST5G	F1027	FCX749	FM_CURRENT
ESD9B5.0ST5G	F1072	FEP16DT-E3/45	FM_VOLTAGE
ESD9C3.3ST5G	F1074	FEP30GP-E3/45	FMMD2835
ESD9C5.0ST5G	F1120	FEP30JPE3/45	FMMD2836
ESD9L5.0ST5G	F1174	FES16BT-E3/45	FMMD2837
ESD9X12ST5G	F1214		FMMD2838

Multisim 14.1 Education Components

FMMD6050	FMMTA20	FS50R12W2T4	FZT1147A
FMMD6100	FMMTA70	FS75R12W2T4	FZT1149A
FMMD7000	FMMTH10	FSK_VOLTAGE	FZT1151A
FMMD914	FMMV105G	FULL_ADDER	FZT604
FMMT38B	FMMV109	FULL_CM	FZT605
FMMT489	FMMV2101	FULL_VM	FZT649
FMMT491A	FMMV2102	FUSE	FZT651
FMMT497	FMMV2103	FUSE_RATED	FZT653
FMMT5179	FMMV2104	FUSE_VIRTUAL	FZT657
FMMT549	FMMV2105	FW344A-TL-2W	FZT658
FMMT589	FMMV2106	FW389-TL-2W	FZT688B
FMMT591A	FMMV2107	FW4604-TL-2W	FZT689B
FMMT597	FMMV2108	FWDCCM	FZT690B
FMMT597Q	FMMV2109	FWDDCM	FZT692B
FMMT617	FMMV3102	FX2-100S- 1.27DS(71)	FZT694B
FMMT618	FOOT_NC		FZT696B
FMMT619	FOOT_NO	FX8-120P-SV1(91)	FZT705
FMMT624	FORWARDCM	FX8-120S-SV(21)	FZT749
FMMT625	FORWARDVM	FZ600R12KE4	FZT751
FMMT717	FREQ_DIVIDER	FZ900R12KP4	FZT753
FMMT718	FREQUENCY_TABLE	FZT1047A	FZT757
FMMT720	_FUNCTION	FZT1048A	FZT758
FMMT722	FS100R12KT4	FZT1049A	FZT788A
FMMT723	FS150R12KT4	FZT1051A	FZT788B
FMMT918	FS25R12W1T4	FZT1053A	FZT789A

Multisim 14.1 Education Components

FZT790A	GBU6M-E3/45	GL34D	GLL4756
FZT792A	GEARS	GL34G	GLL4757
FZT795A	GEN_CNTR_4ABIN	GL34G-E3/98	GLL4758
FZT796A	GF1A	GL34J	GLL4759
FZT849	GF1B	GLL4735	GLL4760
FZT851	GF1D	GLL4736	GLL4761
FZT857	GF1G	GLL4737	GLL4762
FZT869	GF1G-E3/67A	GLL4738	GLL4763
FZT948	GF1J	GLL4739	GP02-20
FZT949	GF1K	GLL4740	GP02-25
FZT951	GF1M	GLL4741	GP02-30
FZT953	GI250-1	GLL4742	GP02-35
FZT955	GI250-2	GLL4743	GP02-40
FZT956	GI250-3	GLL4744	GP02-40-E3/54
FZT957	GI250-4	GLL4745	GP08A
FZT958	GI751-E3/54	GLL4746	GP08B
FZT968	GI810	GLL4747	GP08D
G3SBA60-E3/51	GI811	GLL4748	GP08G
GaAsFET_N	GI812	GLL4749	GP08J
GaAsFET_P	GI814	GLL4750	GP10A
GAIN_2_PIN	GI816	GLL4751	GP10B
GBPC3506W-E4/51	GI817	GLL4752	GP10D
GBU4G-E3/45	GI818	GLL4753	GP10G
GBU4M-E3/51	GL34A	GLL4754	GP10J
GBU6G-E3/45	GL34B	GLL4755	GP10K

Multisim 14.1 Education Components

GP10M	GP30K	HA1-2840-5	HA2-2542-2
GP10N	GP30M	HA1-2840-9	HA2-2542-5
GP10Q	GRAPH_LCD_L	HA1-2850-5	HA2-2544-2
GP10T	GRAPH_LCD_M	HA1-2850-9	HA2-2548-5
GP10V	GRAPH_LCD_S	HA1-4741-2	HA2-2548-9
GP10W	GROUND	HA1-4741-5	HA2-2600-2
GP10Y	GROUND_REF1	HA1-5104-2	HA2-2602-2
GP10Y-E3/54	GROUND_REF2	HA1-5104-5	HA2-2605-5
GP15A	GROUND_REF3	HA1-5114-2	HA2-2620-2
GP15B	GROUND_REF4	HA1-5114-5	HA2-2622-2
GP15D	GROUND_REF5	HA1-5134-2	HA2-2625-5
GP15G	GSB311A41EU	HA1-5134-5	HA2-2640-2
GP15J	GSB3211311WEU	HA1-5190-2	HA2-5101-2
GP15K	GSIB1580-E3/45	HA2-2500-2	HA2-5102-2
GP15M	GSIB2560-E3/45	HA2-2502-2	HA2-5102-5
GP20A	GTO	HA2-2510-2	HA2-5130-5
GP20B	HA1-2539-2	HA2-2512-2	HA2-5135-5
GP20D	HA1-2539-5	HA2-2515-2	HA2-5142-2
GP20G	HA1-2540-2	HA2-2520-2	HA2-5142-5
GP20J	HA1-2540-5	HA2-2522-2	HA2-5147-2
GP30A	HA1-2541-2	HA2-2525-5	HA2-5147-5
GP30B	HA1-2541-5	HA2-2529-2	HA2-5160-2
GP30D	HA1-2542-2	HA2-2529-5	HA2-5160-5
GP30G	HA1-2542-5	HA2-2541-2	HA2-5162-5
GP30J	HA1-2839-5	HA2-2541-5	HA2-5170-2

Multisim 14.1 Education Components

HA2-5170-5	HA3-2841-9	HA3B2840-5	HA7-2625-5
HA2-5190-2	HA3-2842-5	HA3B2840-9	HA7-2640-2
HA2-5221-5	HA3-2842-9	HA3B2841-5	HA7-2645-5
HA2-7712A-5	HA3-2850-5	HA3B2841-9	HA7-2840-5
HA2-7712A-9	HA3-2850-9	HA3B2842-5	HA7-2840-9
HA2-7712B-5	HA3-4741-5	HA3B2842-9	HA7-2850-5
HA2-7712B-9	HA3-5101-5	HA3B2850-5	HA7-2850-9
HA3-2444-5	HA3-5102-5	HA3B2850-9	HA7-5101-2
HA3-2444-9	HA3-5104-5	HA4P2525-5	HA7-5102-2
HA3-2525-5	HA3-5111-5	HA7-2500-2	HA7-5102-5
HA3-2529-5	HA3-5112-5	HA7-2510-2	HA7-5111-2
HA3-2539-5	HA3-5114-5	HA7-2512-2	HA7-5112-2
HA3-2539C-5	HA3-5127-5	HA7-2515-2	HA7-5127-2
HA3-2540-5	HA3-5127A-5	HA7-2520-2	HA7-5127-5
HA3-2542-5	HA3-5142-5	HA7-2522-2	HA7-5127A-2
HA3-2544-5	HA3-5147-5	HA7-2525-5	HA7-5127A-5
HA3-2544C-5	HA3-5177-5	HA7-2529-5	HA7-5130-2
HA3-2548-5	HA3-5221-5	HA7-2544-2	HA7-5130-5
HA3-2605-5	HA3-5222-5	HA7-2544-5	HA7-5135-2
HA3-2625-5	HA3-5232-5	HA7-2548-5	HA7-5135-5
HA3-2839-5	HA3-5232-9	HA7-2600-2	HA7-5137-2
HA3-2839-9	HA3-7712A-5	HA7-2602-2	HA7-5137-5
HA3-2840-5	HA3-7712A-9	HA7-2605-5	HA7-5142-2
HA3-2840-9	HA3-7712B-5	HA7-2620-2	HA7-5142-5
HA3-2841-5	HA3-7712B-9	HA7-2622-2	HA7-5147-2

Multisim 14.1 Education Components

HA7-5147-5	HA9P2842-5	HA9P7712B-5	HCNR201
HA7-5170-2	HA9P2842-9	HA9P7712B-9	HCNW136-000E
HA7-5170-5	HA9P2850-5	HALF_ADDER	HCNW136-300E
HA7-5177-5	HA9P2850-9	HALF_CM	HCNW139-000E
HA7-5221-5	HA9P4741-9	HALF_VM	HCNW139-300E
HA7-5221-9	HA9P5101-5	HC-49/U_1.5MHz	HCNW2201-000E
HA7-5222-5	HA9P5101-9	HC-49/U_11MHz	HCNW2201-300E
HA7-5222-9	HA9P5102-5	HC-49/U_15MHz	HCNW3120-000E
HA9P2444-5	HA9P5102-9	HC-49/U_25MHz	HCNW3120-300E
HA9P2444-9	HA9P5104-5	HC-49/U_3MHz	HCPL-0201-000E
HA9P2529-5	HA9P5104-9	HC-49/U_40MHz	HCPL-0201-060E
HA9P2539-5	HA9P5111-5	HC-49/U_5MHz	HCPL-0211-000E
HA9P2539-9	HA9P5111-9	HC-49/U_7MHz	HCPL-0211-060E
HA9P2540-5	HA9P5112-5	HC-49/U_80MHz	HCPL-0302-000E
HA9P2544-5	HA9P5112-9	HC-49/US_11MHz	HCPL-0302-060E
HA9P2544-9	HA9P5114-5	HC-49/US_15MHz	HCPL-0314-000E
HA9P2544C-5	HA9P5114-9	HC-49/US_25MHz	HCPL-0314-060E
HA9P2544C-9	HA9P5127-5	HC-49/US_40MHz	HCPL-0454-000E
HA9P2548-5	HA9P5137-5	HC-49/US_5MHz	HCPL-0454-060E
HA9P2605-5	HA9P5142-9	HC-49/US_7MHz	HCPL-0466-000E
HA9P2625-5	HA9P5221-5	HCNR200	HCPL-0466-060E
HA9P2840-5	HA9P5222-5	HCNR200-000E	HCPL-0501-500E
HA9P2840-9	HA9P5222-9	HCNR200-050E	HCPL-0501-560E
HA9P2841-5	HA9P5232-5	HCNR200-300E	HCPL0631
HA9P2841-9	HA9P5232-9	HCNR200-350E	HCPL-063L-000E

Multisim 14.1 Education Components

HCPL-063L-060E	HCPL-2219-300E	HCPL-4504-020E	HDR1X15
HCPL-0701-000E	HCPL-2219-360E	HCPL-4504-060E	HDR1X16
HCPL-0701-060E	HCPL-2231-000E	HCPL-4504-300E	HDR1X17
HCPL-181-000E	HCPL-2231-300E	HCPL-4504-320E	HDR1X18
HCPL-181-060E	HCPL-2232-000E	HCPL-4504-360E	HDR1X19
HCPL-2200-000E	HCPL-2232-300E	HCPL-4506-000E	HDR1X2
HCPL-2200-300E	HCPL-263L-000E	HCPL-4506-020E	HDR1X20
HCPL-2201-000E	HCPL-263L-020E	HCPL-4506-060E	HDR1X21
HCPL-2201-060E	HCPL-263L-060E	HCPL-4506-300E	HDR1X22
HCPL-2201-300E	HCPL-263L-300E	HCPL-4506-320E	HDR1X23
HCPL-2201-360E	HCPL-263L-320E	HCPL-4506-360E	HDR1X24
HCPL-2202-000E	HCPL-263L-560E	HCPL-7510-000E	HDR1X25
HCPL-2202-060E	HCPL-3020-000E	HCPL-7510-060E	HDR1X3
HCPL-2202-300E	HCPL-3020-060E	HCPL-7510-300E	HDR1X4
HCPL-2202-360E	HCPL-3020-300E	HCPL-7510-360E	HDR1X5
HCPL-2211-000E	HCPL-3120-000E	HCPL-7800-000E	HDR1X6
HCPL-2211-060E	HCPL-3120-060E	HCPL-7800-300E	HDR1X7
HCPL-2211-300E	HCPL-3120-300E	HCPL-J312-000E	HDR1X8
HCPL-2211-360E	HCPL-3120-360E	HCPL-J312-300E	HDR1X9
HCPL-2212-000E	HCPL-3140-000E	HD4A	HDR2X10
HCPL-2212-060E	HCPL-3140-060E	HDR1X10	HDR2X11
HCPL-2212-300E	HCPL-3140-300E	HDR1X11	HDR2X12
HCPL-2212-360E	HCPL-3140-360E	HDR1X12	HDR2X13
HCPL-2219-000E	HCPL-316J-000E	HDR1X13	HDR2X14
HCPL-2219-060E	HCPL-4504-000E	HDR1X14	HDR2X15

Multisim 14.1 Education Components

HDR2X16	HEL-711-T012	HF50ACC322513	HFA35HB120
HDR2X17	HEL-711-U012	HF50ACC453215	HFA45HC60C
HDR2X18	HEL-712-T012	HF70ACC201209	HFA7-0002-5
HDR2X19	HEL-712-U012	HF70ACC321611	HFA7-0002-9
HDR2X2	HEL-716-T012	HF70ACC322513	HFA7-0005-5
HDR2X20	HEL-716-U012	HF70ACC453215	HFA7-0005-9
HDR2X21	HEL-717-T012	HFA04TB60	HFA9P0001-5
HDR2X22	HEL-717-U012	HFA08PB120	HFA9P0002-5
HDR2X23	HEL-775-AT0	HFA08TB60	HFA9P0002-9
HDR2X24	HEL-775-AU0	HFA1-0001-5	HFA9P0005-5
HDR2X25	HEL-775-BT0	HFA1-0001-9	HFA9P0005-9
HDR2X3	HEL-775-BU0	HFA15TB60	HFB16HY20C
HDR2X4	HEL-776-AT0	HFA16PB120	HFB20HJ20C
HDR2X5	HEL-776-AU0	HFA2-0002-5	HFB25HJ20
HDR2X6	HEL-777-AT0	HFA2-0002-9	HFB35HB20
HDR2X7	HEL-777-AU0	HFA2-0005-5	HFB35HB20C
HDR2X8	HELD_CLOSED_LIMIT	HFA2-0005-9	HFB50HC20
HDR2X9	HELD_OPEN_LIMIT	HFA25TB60	HFB50HC20C
HEL-700-T0A	HF30ACC201209	HFA3-0001-5	HFB50HI20
HEL-700-T0B	HF30ACC321611	HFA3-0001-9	HFB50HI20C
HEL-700-U0A	HF30ACC322513	HFA3-0002-5	HFB60HF20
HEL-700-U0B	HF30ACC453215	HFA3-0002-9	HFB60HF20C
HEL-700-U0C	HF50ACC201209	HFA3-0005-5	HM1-65642-883
HEL-705-U012	HF50ACC321611	HFA3-0005-9	HM1-65642B-883
HEL-707-U012		HFA30PA60C	HM1-65642C-883

Multisim 14.1 Education Components

HM4-65642-883	ICL7652	IDB45E60	IDH06G65C5
HM4-65642B-883	ICL7652D	IDD03E60	IDH06S60C
HM6116A120	ICL7652P	IDD03SG60C	IDH06SG60C
HOLDING_TANK	ICM7555ESA+	IDD04SG60C	IDH08G120C5
HRTS-5760-BU012	ICM7555IJA+	IDD05SG60C	IDH08G65C5
HRTS-61-T024	ICM7555IPA+	IDD06E60	IDH08S120
HRTS-61-U024	ICM7555ISA+	IDD06SG60C	IDH08S60C
HSDL-5400	ICM7555ITV	IDD08SG60C	IDH08SG60C
HSDL-5420	ICM7555MJA	IDD09E60	IDH09G65C5
HSDL-5420#031	ICM7555MTV	IDD09SG60C	IDH09SG60C
ICL7611ACPA	ICM7556IPD+	IDD10SG60C	IDH10G120C5
ICL7611ACTV	ICM7556ISD+	IDD12SG60C	IDH10G65C5
ICL7611AMTV	ICM7556MJD+	IDD15E60	IDH10S120
ICL7611DCBA	IDAC	IDD23E60	IDH10S60C
ICL7650SCBA-1	IDAC16	IDH02G120C5	IDH10SG60C
ICL7650SCBD	IDB04E120	IDH02G65C5	IDH12G65C5
ICL7650SCPA	IDB06E60	IDH02SG120	IDH12S60C
ICL7650SCPD	IDB09E120	IDH03G65C5	IDH15S120
ICL7650SCTV-1	IDB09E60	IDH04G65C5	IDH16G120C5
ICL7650SIJD	IDB12E120	IDH04S60C	IDH16G65C5
ICL7650SIPA-1	IDB15E60	IDH04SG60C	IDH16S60C
ICL7650SIPD	IDB18E120	IDH05G65C5	IDH20G120C5
ICL7650SITV-1	IDB23E60	IDH05S120	IDH20G65C5
ICL7650SMJD	IDB30E120	IDH05S60C	IDK02G65C5
ICL7650SMTV-1	IDB30E60	IDH05SG60C	IDK03G65C5

Multisim 14.1 Education Components

IDK04G65C5	IDP30E60	INA133U	INA199A1DCKR
IDK05G65C5	IDP45E60	INA133UA	INA199A1RSWR
IDK06G65C5	IDW100E60	INA138NA	INA199A2DCKR
IDK08G65C5	IDW10G120C5B	INA143U	INA199A2RSWR
IDK09G65C5	IDW10G65C5	INA143UA	INA199A3DCKR
IDK10G65C5	IDW10S120	INA145UA	INA199A3RSWR
IDK12G65C5	IDW12G65C5	INA146UA	INA200AID
IDL02G65C5	IDW15G120C5B	INA148UA	INA200AIDGKR
IDL04G65C5	IDW15S120	INA152EA/250	INA201AID
IDL06G65C5	IDW16G65C5	INA154U	INA201AIDGKR
IDL08G65C5	IDW20G120C5B	INA154UA	INA202AID
IDL10G65C5	IDW20G65C5	INA157U	INA202AIDGKR
IDL12G65C5	IDW20S120	INA157UA	INA203AID
IDM02G120C5	IDW30G120C5B	INA159AID	INA203AIPW
IDM08G120C5	IDW30G65C5	INA163UA	INA206AID
IDM10G120C5	IDW30S120	INA168NA	INA206AIPW
IDP04E120	IDW40G120C5B	INA169NA	INA207AID
IDP06E60	IDW40G65C5	INA170EA	INA207AIPW
IDP09E120	IDW75E60	INA188ID	INA208AID
IDP09E60	IGBT_DIODE_THERMAL	INA193AID	INA208AIPW
IDP12E120	IJW120R070T1	INA193AIDBVT	INA210AIDCKR
IDP15E60	IJW120R100T1	INA194AID	INA210AIRSWR
IDP18E120	ILLUMINATED_PB	INA194AIDBVT	INA210BIDCKR
IDP23E60	INA105_CMP	INA195AID	INA210BIRSWR
IDP30E120		INA195AIDBVT	INA211AIDCKR

Multisim 14.1 Education Components

INA211BIDCKR	INA225AIDGKR	INA333AIDGKR	INPUT_MODULE_1 2Vdc
INA2126E/250	INA270AID	INA333AIDRGR	INPUT_MODULE_2 40Vdc
INA2126EA/250	INA271AID	INCREMENTAL_ENC ODER	INPUT_MODULE_2 4Vdc
INA2126P	INA282AID	INDICATOR	INPUT_MODULE_3 0Vdc
INA2126U	INA282AIDGKT	INDUCTION_MACHI NE_SQUIRREL_CAG E	INPUT_MODULE_5 Vdc
INA212AIDCKR	INA283AID	INDUCTION_MACHI NE_SQUIRREL_CAG E_E	INPUT_MODULE_9 Vdc
INA212BIDCKR	INA283AIDGKT	INDUCTION_MACHI NE_WOUND	INTERACTIVE_DIGIT AL_CONSTANT
INA2132U	INA284AID	INDUCTION_MACHI NE_WOUND_E	INV
INA213AIDCKR	INA285AID	INDUCTOR_COUPLI NG	IPA028N08N3 G
INA213AIDCKT	INA285AIDGKT	Inductor_Lossy	IPA029N06N
INA213AIRSWR	INA286AID	INDUCTOR_RATED	IPA030N10N3 G
INA213BIDCKR	INA286AIDGKT	INDUCTOR_VIRTUA L	IPA032N06N3 G
INA213BIRSWR	INA300AIDSQR	Inductor1_1.0uH	IPA037N08N3 G
INA214AIDCKR	INA301A1IDGKT	Inductor2_1.0uH	IPA040N06N
INA214AIRSWR	INA301A2IDGKT	INERTIAL_LOAD	IPA041N04N G
INA214BIDCKR	INA301A3IDGKT	INPUT_CONTACT_N C	IPA045N10N3 G
INA214BIRSWR	INA321E	INPUT_CONTACT_N O	IPA057N06N3 G
INA215AIDCKR	INA321EA	INPUT_MODULE_1 20Vdc	IPA057N08N3 G
INA216A2RSWR	INA322EA		IPA060N06N
INA216A2YFFR	INA326EA		IPA075N15N3 G
INA216A3RSWR	INA327EA		IPA083N10N5
INA216A3YFFR	INA331AIDGK		
INA216A4RSWR	INA331IDGK		
INA216A4YFFR	INA332IDGK		

Multisim 14.1 Education Components

IPA086N10N3 G	IPA60R160C6	IPA60R950C6	IPB010N06N
IPA093N06N3 G	IPA60R160P6	IPA65R045C7	IPB011N04L G
IPA100N08N3 G	IPA60R165CP	IPA65R065C7	IPB011N04N G
IPA105N15N3 G	IPA60R190C6	IPA65R095C7	IPB014N06N
IPA126N10N3 G	IPA60R190E6	IPA65R125C7	IPB015N04L G
IPA180N10N3 G	IPA60R190P6	IPA65R190C6	IPB015N04N G
IPA50R140CP	IPA60R199CP	IPA65R190C7	IPB015N08N5
IPA50R190CE	IPA60R230P6	IPA65R190CFD	IPB016N06L3 G
IPA50R199CP	IPA60R250CP	IPA65R190E6	IPB017N06N3 G
IPA50R250CP	IPA60R280C6	IPA65R225C7	IPB017N08N5
IPA50R280CE	IPA60R280E6	IPA65R280C6	IPB017N10N5
IPA50R299CP	IPA60R280P6	IPA65R280E6	IPB019N06L3 G
IPA50R350CP	IPA60R299CP	IPA65R310CFD	IPB019N08N3 G
IPA50R380CE	IPA60R330P6	IPA65R380C6	IPB020N04N G
IPA50R399CP	IPA60R380C6	IPA65R380E6	IPB020N08N5
IPA50R500CE	IPA60R380E6	IPA65R420CFD	IPB020N10N5
IPA50R520CP	IPA60R380P6	IPA65R600C6	IPB020NE7N3 G
IPA50R650CE	IPA60R385CP	IPA65R600E6	IPB021N06N3 G
IPA50R800CE	IPA60R450E6	IPA65R660CFD	IPB022N04L G
IPA50R950CE	IPA60R520C6	IPA90R1K0C3	IPB023N04N G
IPA60R099C6	IPA60R520E6	IPA90R1K2C3	IPB023N06N3 G
IPA60R099P6	IPA60R600C6	IPA90R340C3	IPB024N08N5
IPA60R125C6	IPA60R600E6	IPA90R500C3	IPB025N08N3 G
IPA60R125CP	IPA60R600P6	IPA90R800C3	IPB025N10N3 G
IPA60R125P6	IPA60R750E6	IPB009N03L G	IPB026N06N

Multisim 14.1 Education Components

IPB027N10N3 G	IPB054N08N3 G	IPB120N06S4-02	IPB180N10S4-02
IPB027N10N5	IPB055N03L G	IPB120N06S4-03	IPB180N10S4-03
IPB029N06N3 G	IPB057N06N	IPB120N06S4-H1	IPB180P04P4-03
IPB030N08N3 G	IPB065N03L G	IPB120N08S4-03	IPB180P04P4L-02
IPB031N08N5	IPB065N10N3 G	IPB120N08S4-04	IPB200N15N3 G
IPB031NE7N3 G	IPB065N15N3 G	IPB120N10S4-03	IPB200N25N3 G
IPB034N03L G	IPB067N08N3 G	IPB120P04P4-04	IPB230N06L3 G
IPB034N06L3 G	IPB072N15N3 G	IPB120P04P4L-03	IPB240N04S4-1R0
IPB034N06N3 G	IPB075N04L G	IPB123N10N3 G	IPB240N04S4-R9
IPB035N08N3 G	IPB080N03L G	IPB136N08N3 G	IPB260N06N3 G
IPB036N12N3 G	IPB081N06L3 G	IPB140N08S4-04	IPB26CN10N G
IPB037N06N3 G	IPB083N10N3 G	IPB144N12N3 G	IPB320N20N3 G
IPB038N12N3 G	IPB090N06N3 G	IPB147N03L G	IPB34CN10N G
IPB039N04L G	IPB093N04L G	IPB160N04S4-H1	IPB407N30N
IPB039N10N3 G	IPB096N03L G	IPB160N04S4L-H1	IPB45P03P4L-11
IPB041N04N G	IPB097N08N3 G	IPB160N08S4-03	IPB50CN10N G
IPB042N03L G	IPB100N04S4-H2	IPB180N03S4L-01	IPB50N10S3L-16
IPB042N10N3 G	IPB107N20N3 G	IPB180N03S4L-H0	IPB50R140CP
IPB048N06L G	IPB107N20NA	IPB180N04S4-00	IPB50R199CP
IPB049N06L3 G	IPB108N15N3 G	IPB180N04S4-01	IPB50R250CP
IPB049N08N5	IPB114N03L G	IPB180N04S4-H0	IPB50R299CP
IPB049NE7N3 G	IPB117N20NFD	IPB180N04S4L-01	IPB530N15N3 G
IPB050N06N G	IPB120N04S4-01	IPB180N04S4L-H0	IPB600N25N3 G
IPB052N04N G	IPB120N04S4-02	IPB180N06S4-H1	IPB60R099CP
IPB054N06N3 G	IPB120N04S4L-02	IPB180N08S4-02	IPB60R125CP

Multisim 14.1 Education Components

IPB60R165CP	IPB80N04S4L-04	IPD040N03L G	IPD135N03L G
IPB60R199CP	IPB80N06S4-05	IPD042P03L3 G	IPD135N08N3 G
IPB60R250CP	IPB80N06S4-07	IPD048N06L3 G	IPD144N06N G
IPB60R385CP	IPB80N06S4L-05	IPD050N03L G	IPD160N04L G
IPB65R045C7	IPB80N06S4L-07	IPD053N06N	IPD170N04N G
IPB65R065C7	IPB80N08S4-06	IPD053N06N3 G	IPD180N10N3 G
IPB65R095C7	IPB80P03P4-05	IPD053N08N3 G	IPD200N15N3 G
IPB65R110CFDA	IPB80P03P4L-04	IPD060N03L G	IPD220N06L3 G
IPB65R125C7	IPB80P03P4L-07	IPD068N10N3 G	IPD230N06N G
IPB65R150CFDA	IPB80P04P4-05	IPD068P03L3 G	IPD250N06N3 G
IPB65R190C7	IPB80P04P4-07	IPD075N03L G	IPD25CN10N G
IPB65R190CFD	IPB80P04P4L-04	IPD079N06L3 G	IPD25N06S4L-30
IPB65R190CFDA	IPB80P04P4L-06	IPD082N10N3 G	IPD30N03S4L-14
IPB65R225C7	IPB80P04P4L-08	IPD088N04L G	IPD30N06S4L-23
IPB65R310CFDA	IPB90N04S4-02	IPD088N06N3 G	IPD30N10S3L-34
IPB65R660CFD	IPB90N06S4-04	IPD090N03L G	IPD320N20N3 G
IPB65R660CFDA	IPB90N06S4L-04	IPD096N08N3 G	IPD33CN10N G
IPB70N04S4-06	IPD025N06N	IPD100N04S4-02	IPD350N06L G
IPB70N10S3-12	IPD031N03L G	IPD100N06S4-03	IPD35N10S3L-26
IPB70N10S3L-12	IPD031N06L3 G	IPD105N03L G	IPD400N06N G
IPB70P04P4-09	IPD034N06N3 G	IPD105N04L G	IPD40N03S4L-08
IPB80N03S4L-02	IPD035N06L3 G	IPD110N12N3 G	IPD50N03S4L-06
IPB80N03S4L-03	IPD036N04L G	IPD122N10N3 G	IPD50N04S4-08
IPB80N04S4-03	IPD038N04N G	IPD127N06L G	IPD50N04S4-10
IPB80N04S4-04	IPD038N06N3 G	IPD12CN10N G	IPD50N04S4L-08

Multisim 14.1 Education Components

IPD50N06S4L-08	IPD60R380P6	IPD70N03S4L-04	IPD90P04P4-05
IPD50N06S4L-12	IPD60R385CP	IPD70P04P4-09	IPD90P04P4L-04
IPD50N08S4-13	IPD60R3K3C6	IPD70P04P4L-08	IPD90R1K2C3
IPD50P03P4L-11	IPD60R450E6	IPD75N04S4-06	IPG16N10S4-61
IPD50P04P4-13	IPD60R520C6	IPD78CN10N G	IPG16N10S4L-61A
IPD50P04P4L-11	IPD60R600C6	IPD800N06N G	IPG20N04S4-12
IPD50R1K4CE	IPD60R600E6	IPD80P03P4L-07	IPG20N04S4L-07
IPD50R280CE	IPD60R600P6	IPD85P04P4-07	IPG20N04S4L-08
IPD50R2K0CE	IPD60R750E6	IPD85P04P4L-06	IPG20N04S4L-11
IPD50R380CE	IPD60R950C6	IPD90N03S4L-02	IPG20N10S4-36A
IPD50R399CP	IPD640N06L G	IPD90N03S4L-03	IPG20N10S4L-22
IPD50R3K0CE	IPD65R190C7	IPD90N04S4-02	IPG20N10S4L-35
IPD50R500CE	IPD65R1K4C6	IPD90N04S4-03	IPI020N06N
IPD50R520CP	IPD65R1K4CFD	IPD90N04S4-04	IPI023NE7N3 G
IPD50R650CE	IPD65R225C7	IPD90N04S4-05	IPI024N06N3 G
IPD50R800CE	IPD65R380C6	IPD90N04S4L-04	IPI028N08N3 G
IPD50R950CE	IPD65R380E6	IPD90N06S4-04	IPI029N06N
IPD530N15N3 G	IPD65R420CFD	IPD90N06S4-05	IPI030N10N3 G
IPD600N25N3 G	IPD65R420CFDA	IPD90N06S4-07	IPI032N06N3 G
IPD60N10S4-12	IPD65R600C6	IPD90N06S4L-03	IPI034NE7N3 G
IPD60N10S4L-12	IPD65R600E6	IPD90N08S4-05	IPI037N06L3 G
IPD60R1K4C6	IPD65R660CFD	IPD90N10S4-06	IPI037N08N3 G
IPD60R2K0C6	IPD65R660CFDA	IPD90N10S4L-06	IPI040N06N3 G
IPD60R380C6	IPD65R950C6	IPD90P03P4-04	IPI041N12N3 G
IPD60R380E6	IPD65R950CFD	IPD90P03P4L-04	IPI045N10N3 G

Multisim 14.1 Education Components

IPI04CN10N G	IPI200N25N3 G	IPI80P04P4L-04	IPLU300N04S4-1R1
IPI052NE7N3 G	IPI26CN10N G	IPI90N04S4-02	IPP015N04N G
IPI057N08N3 G	IPI320N20N3 G	IPI90N06S4-04	IPP020N06N
IPI070N08N3 G	IPI35CN10N G	IPI90N06S4L-04	IPP020N08N5
IPI072N10N3 G	IPI45N06S4-09	IPI90R1K0C3	IPP023N04N
IPI075N15N3 G	IPI45N06S4L-08	IPI90R1K2C3	IPP023N04N G
IPI076N12N3 G	IPI50CN10N G	IPI90R500C3	IPP023N08N5
IPI084N06L3 G	IPI50N10S3L-16	IPI90R800C3	IPP023N10N5
IPI086N10N3 G	IPI50R350CP	IPL60R199CP	IPP023NE7N3 G
IPI100N04S4-H2	IPI530N15N3 G	IPL60R299CP	IPP024N06N3 G
IPI100N08N3 G	IPI600N25N3 G	IPL60R360P6S	IPP027N08N5
IPI110N20N3 G	IPI60R250CP	IPL60R385CP	IPP028N08N3 G
IPI111N15N3 G	IPI70N04S4-06	IPL60R650P6S	IPP029N06N
IPI120N04S4-01	IPI70N10S3-12	IPL65R070C7	IPP030N10N3 G
IPI120N04S4-02	IPI70N10S3L-12	IPL65R099C7	IPP030N10N5
IPI120N06S4-02	IPI70P04P4-09	IPL65R130C7	IPP032N06N3 G
IPI120N08S4-03	IPI80CN10N G	IPL65R165CFD	IPP034N03L G
IPI120N08S4-04	IPI80N04S4-03	IPL65R190E6	IPP034N08N5
IPI120N10S4-03	IPI80N04S4-04	IPL65R195C7	IPP034NE7N3 G
IPI120N10S4-05	IPI80N04S4L-04	IPL65R210CFD	IPP037N06L3 G
IPI126N10N3 G	IPI80N06S4-07	IPL65R230C7	IPP037N08N3 G
IPI139N08N3 G	IPI80N08S4-06	IPL65R340CFD	IPP039N04L G
IPI147N12N3 G	IPI80P03P4L-04	IPL65R460CFD	IPP040N06N
IPI180N10N3 G	IPI80P03P4L-07	IPL65R725CFD	IPP040N06N3 G
IPI200N15N3 G	IPI80P04P4-05	IPLU250N04S4-1R7	IPP041N04N G

Multisim 14.1 Education Components

IPP041N12N3 G	IPP085N06L G	IPP16CN10L G	IPP50R500CE
IPP042N03L G	IPP086N10N3 G	IPP16CN10N G	IPP50R520CP
IPP045N10N3 G	IPP08CN10L G	IPP180N10N3 G	IPP530N15N3 G
IPP048N04N G	IPP093N06N3 G	IPP200N15N3 G	IPP600N25N3 G
IPP048N12N3 G	IPP096N03L G	IPP200N25N3 G	IPP60R040C7
IPP04CN10N G	IPP100N04S4-H2	IPP220N25NFD	IPP60R074C6
IPP052N06L3 G	IPP100N08N3 G	IPP230N06L3 G	IPP60R099C6
IPP052N08N5	IPP110N20N3 G	IPP260N06N3 G	IPP60R099C7
IPP052NE7N3 G	IPP110N20NA	IPP26CN10N G	IPP60R099CP
IPP055N03L G	IPP111N15N3 G	IPP320N20N3 G	IPP60R099P6
IPP057N06N3 G	IPP114N03L G	IPP410N30N	IPP60R125C6
IPP057N08N3 G	IPP114N12N3 G	IPP45N06S4-09	IPP60R125CP
IPP05CN10L G	IPP120N04S4-01	IPP45N06S4L-08	IPP60R125P6
IPP05CN10N G	IPP120N06N G	IPP45P03P4L-11	IPP60R160C6
IPP060N06N	IPP120N06S4-H1	IPP50CN10N G	IPP60R160P6
IPP062NE7N3 G	IPP120N08S4-03	IPP50N10S3L-16	IPP60R165CP
IPP065N03L G	IPP120N08S4-04	IPP50R140CP	IPP60R180C7
IPP06CN10L G	IPP120N10S4-03	IPP50R190CE	IPP60R190C6
IPP070N08N3 G	IPP120N10S4-05	IPP50R199CP	IPP60R190E6
IPP072N10N3 G	IPP120N20NFD	IPP50R250CP	IPP60R190P6
IPP075N15N3 G	IPP126N10N3 G	IPP50R280CE	IPP60R199CP
IPP076N12N3 G	IPP12CN10L G	IPP50R299CP	IPP60R1K4C6
IPP080N03L G	IPP139N08N3 G	IPP50R350CP	IPP60R230P6
IPP083N10N5	IPP147N03L G	IPP50R380CE	IPP60R250CP
IPP084N06L3 G	IPP147N12N3 G	IPP50R399CP	IPP60R280C6

Multisim 14.1 Education Components

IPP60R280E6	IPP65R190C6	IPP80P03P4L-04	IPT059N15N3
IPP60R280P6	IPP65R190C7	IPP80P03P4L-07	IPU135N08N3 G
IPP60R299CP	IPP65R190CFD	IPP80P04P4L-04	IPU50R1K4CE
IPP60R330P6	IPP65R190CFDA	IPP90R1K0C3	IPU50R2K0CE
IPP60R380C6	IPP65R190E6	IPP90R1K2C3	IPU50R3K0CE
IPP60R380E6	IPP65R225C7	IPP90R340C3	IPU50R950CE
IPP60R380P6	IPP65R280C6	IPP90R500C3	IPW50R190CE
IPP60R385CP	IPP65R280E6	IPP90R800C3	IPW50R199CP
IPP60R450E6	IPP65R310CFD	IPS031N03L G	IPW50R280CE
IPP60R520C6	IPP65R310CFDA	IPS040N03L G	IPW60R040C7
IPP60R520E6	IPP65R380C6	IPS050N03L G	IPW60R041C6
IPP60R600C6	IPP65R380E6	IPS060N03L G	IPW60R041P6
IPP60R600E6	IPP65R420CFD	IPS075N03L G	IPW60R045CP
IPP60R600P6	IPP65R600C6	IPS090N03L G	IPW60R070C6
IPP60R750E6	IPP65R600E6	IPS105N03L G	IPW60R070P6
IPP60R950C6	IPP65R660CFD	IPS110N12N3 G	IPW60R075CP
IPP65R045C7	IPP65R660CFDA	IPS118N10N G	IPW60R099C6
IPP65R065C7	IPP70N04S4-06	IPS12CN10L G	IPW60R099C7
IPP65R074C6	IPP70N10S3L-12	IPS135N03L G	IPW60R099CP
IPP65R095C7	IPP80CN10N G	IPS50R520CP	IPW60R099P6
IPP65R099C6	IPP80N04S4-03	IPT004N03L	IPW60R125C6
IPP65R110CFD	IPP80N04S4-04	IPT007N06N	IPW60R125CP
IPP65R110CFDA	IPP80N04S4L-04	IPT012N08N5	IPW60R125P6
IPP65R125C7	IPP80N06S4-07	IPT015N10N5	IPW60R160C6
IPP65R150CFDA	IPP80N08S4-06	IPT020N10N3	IPW60R160P6

Multisim 14.1 Education Components

IPW60R165CP	IPW65R190C6	IR2102SPBF	IR2127PBF
IPW60R180C7	IPW65R190C7	IR2103PBF	IR2127SPBF
IPW60R190C6	IPW65R190CFDA	IR2103SPBF	IR2128PBF
IPW60R190E6	IPW65R190E6	IR2104PBF	IR2128SPBF
IPW60R190P6	IPW65R280C6	IR2104SPBF	IR21363JPBF
IPW60R199CP	IPW65R280E6	IR2106PBF	IR21363PBF
IPW60R230P6	IPW90R120C3	IR2106SPBF	IR21363SPBF
IPW60R250CP	IPW90R1K0C3	IR21084PBF	IR21365PBF
IPW60R280C6	IPW90R1K2C3	IR21084SPBF	IR21365SPBF
IPW60R280E6	IPW90R340C3	IR2108PBF	IR2136JPBF
IPW60R280P6	IPW90R500C3	IR2108SPBF	IR2136PBF
IPW60R330P6	IPW90R800C3	IR21094PBF	IR2136SPBF
IPW65R019C7	IPZ60R040C7	IR21094SPBF	IR2181PBF
IPW65R037C6	IPZ60R099C7	IR2109PBF	IR2181SPBF
IPW65R041CFD	IPZ65R019C7	IR2109SPBF	IR2183PBF
IPW65R045C7	IPZ65R045C7	IR2110PBF	IR2183SPBF
IPW65R048CFDA	IPZ65R065C7	IR2110SPBF	IR2184PBF
IPW65R065C7	IPZ65R095C7	IR2112PBF	IR2184SPBF
IPW65R070C6	IR2010PBF	IR2112SPBF	IR2301PBF
IPW65R080CFD	IR2010S	IR2113PBF	IR2301SPBF
IPW65R080CFDA	IR2010SPBF	IR2113SPBF	IR2302PBF
IPW65R095C7	IR2011PBF	IR2117PBF	IR2302SPBF
IPW65R110CFDA	IR2101PBF	IR2117SPBF	IRF100B201
IPW65R125C7	IR2101SPBF	IR2118PBF	IRF100B202
IPW65R150CFDA	IR2102PBF	IR2118SPBF	IRF1010N

Multisim 14.1 Education Components

IRF1010NS	IRF2903ZSTRLP	IRF5210S	IRF6618
IRF1010ZPBF	IRF3205	IRF530	IRF6620
IRF1010ZSPBF	IRF3205S	IRF530S	IRF6621
IRF1010ZSTRLPBF	IRF3205ZL	IRF5305S	IRF6622
IRF1010ZSTRRPBF	IRF3610S	IRF530N	IRF6623
IRF1310	IRF3704ZSPBF	IRF530NS	IRF6628
IRF1310NS	IRF3707ZSPBF	IRF540	IRF6631
IRF1324S-7PPBF	IRF3708	IRF540N	IRF6635
IRF1324STRL-7PP	IRF3709ZSTRRPBF	IRF540NS	IRF6636
IRF1404ZPBF	IRF3710	IRF540ZL	IRF6637
IRF1407	IRF3710S	IRF541	IRF6641TRPBF
IRF1503S	IRF3710ZL	IRF5801	IRF6643TRPBF
IRF1607	IRF3805S-7PPBF	IRF5802	IRF6644TRPBF
IRF200B211	IRF3805STRL-7PP	IRF5803	IRF6645TRPBF
IRF250	IRF3808	IRF5805	IRF6646TRPBF
IRF2505S	IRF40B207	IRF60DM206	IRF6648TRPBF
IRF2804PBF	IRF40H210	IRF6201PBF	IRF6655TRPBF
IRF2804SPBF	IRF40R207	IRF6201TRPBF	IRF6665
IRF2804STRLPBF	IRF4104PBF	IRF6216	IRF6668TRPBF
IRF2804STRRPBF	IRF4104S	IRF6217	IRF6674TRPBF
IRF2805S	IRF510	IRF640NS	IRF6710S2TRPBF
IRF2807S	IRF520	IRF6613TRPBF	IRF6711STRPBF
IRF2807Z	IRF520N	IRF6614TRPBF	IRF6712STRPBF
IRF2807ZS	IRF520NS	IRF6616TRPBF	IRF6713STRPBF
IRF2903ZSPBF	IRF5210	IRF6617	IRF6714MTRPBF

Multisim 14.1 Education Components

IRF6715MTRPBF	IRF7324	IRF7483M	IRF7831
IRF6716MTRPBF	IRF7328	IRF7493	IRF7832
IRF6717MTRPBF	IRF7351	IRF7495PBF	IRF7834
IRF6718L2TRPBF	IRF7380	IRF7495TRPBF	IRF7853
IRF6721S	IRF7401	IRF7501	IRF7855PBF
IRF6724M	IRF7403	IRF7580M	IRF7855TRPBF
IRF6725M	IRF7404	IRF7601	IRF7862
IRF6726M	IRF7406	IRF7606	IRF7902
IRF6727MTRPBF	IRF7413	IRF7607	IRF7907PBF
IRF6775MTRPBF	IRF7413Z	IRF7726	IRF7907TRPBF
IRF6785MTRPBF	IRF7424	IRF7739L1TRPBF	IRF7946TRPBF
IRF6795MTRPBF	IRF7425	IRF7748L1TRPBF	IRF8010
IRF6797MTRPBF	IRF7450	IRF7749L1TRPBF	IRF8010S
IRF6798MTRPBF	IRF7451	IRF7759L2TRPBF	IRF8113
IRF6810STRPBF	IRF7452	IRF7769L1TRPBF	IRF830
IRF6811STRPBF	IRF7455	IRF7779L2TRPBF	IRF8301M
IRF6893MTRPBF	IRF7456	IRF7799L2TRPBF	IRF8302MTRPBF
IRF6894MTRPBF	IRF7457	IRF7807V	IRF8327STRPBF
IRF6898MTRPBF	IRF7463	IRF7807Z	IRF840
IRF7201	IRF7465	IRF7809AV	IRF8513TRPBF
IRF7204	IRF7469	IRF7811AV	IRF8707PBF
IRF7240	IRF7470	IRF7815PBF	IRF8707TRPBF
IRF7307	IRF7473	IRF7815TRPBF	IRF8714PBF
IRF7311	IRF7476	IRF7820	IRF8714TRPBF
IRF7317	IRF7480M	IRF7821	IRF8721PBF

Multisim 14.1 Education Components

IRF8721TRPBF	IRF9395MTRPBF	IRFB4229PBF	IRFB7734
IRF8734PBF	IRF9410	IRFB42N20D	IRFB7740
IRF8734TRPBF	IRF9530	IRFB4310ZPBF	IRFB7746
IRF8736PBF	IRF9530N	IRFB4321PBF	IRFB7787
IRF8736TRPBF	IRF9540NL	IRFB4332PBF	IRFBA1405P
IRF8788PBF	IRF9540NS	IRFB4610PBF	IRFBA90N20D
IRF8788TRPBF	IRF9910	IRFB4615PBF	IRFE130
IRF8915	IRF9Z24N	IRFB4620PBF	IRFF110
IRF9310PBF	IRFB3004PBF	IRFB4710	IRFG110
IRF9310TRPBF	IRFB3006PBF	IRFB5615PBF	IRFH3702
IRF9317PBF	IRFB3077PBF	IRFB5620PBF	IRFH3707
IRF9317TRPBF	IRFB31N20D	IRFB59N10D	IRFH4201TRPBF
IRF9321PBF	IRFB3206PBF	IRFB61N15D	IRFH4210DTRPBF
IRF9321TRPBF	IRFB3207ZPBF	IRFB7430PBF	IRFH4210TRPBF
IRF9328PBF	IRFB3256PBF	IRFB7434PBF	IRFH4213DTRPBF
IRF9328TRPBF	IRFB3306PBF	IRFB7437PBF	IRFH4213TRPBF
IRF9333PBF	IRFB3307ZPBF	IRFB7440PBF	IRFH4234TRPBF
IRF9333TRPBF	IRFB38N20D	IRFB7446PBF	IRFH4251DTRPBF
IRF9335PBF	IRFB4019	IRFB7530PBF	IRFH4253DTRPBF
IRF9335TRPBF	IRFB4020PBF	IRFB7534PBF	IRFH5004
IRF9362PBF	IRFB4110PBF	IRFB7537PBF	IRFH5006TRPBF
IRF9362TRPBF	IRFB4115PBF	IRFB7540PBF	IRFH5007
IRF9383MTRPBF	IRFB4137PBF	IRFB7545PBF	IRFH5010TRPBF
IRF9389PBF	IRFB4227PBF	IRFB7546PBF	IRFH5020TRPBF
IRF9389TRPBF	IRFB4228PBF	IRFB7730	IRFH5025TRPBF

Multisim 14.1 Education Components

IRFH5053	IRFH7545	IRFHM830DTRPBF	IRFI5305
IRFH5106TRPBF	IRFH7787	IRFHM830TRPBF	IRFI530N
IRFH5110TRPBF	IRFH7914	IRFHM831TRPBF	IRFI540N
IRFH5204TRPBF	IRFH7921	IRFHM8326TRPBF	IRFI7440GPBF
IRFH5206TRPBF	IRFH7932	IRFHM8330TRPBF	IRFI7446GPBF
IRFH5207TRPBF	IRFH7934	IRFHM8334TRPBF	IRFI7536GPBF
IRFH5210TRPBF	IRFH7936	IRFHM8337TRPBF	IRFI840G
IRFH5215TRPBF	IRFH8201TRPBF	IRFHM8342	IRFI840GLC
IRFH5250D	IRFH8202	IRFHM8363TRPBF	IRFIZ44N
IRFH5300	IRFH8303	IRFHM9391TRPBF	IRFIZ46N
IRFH5301TRPBF	IRFH8307	IRFHS8242TRPBF	IRFIZ48N
IRFH5302D	IRFH8318TRPBF	IRFHS8342TRPBF	IRFL024Z
IRFH5302TRPBF	IRFH8321	IRFHS9301TRPBF	IRFL4105
IRFH5304TRPBF	IRFH8324TRPBF	IRFHS9351TRPBF	IRFL4310
IRFH5406TRPBF	IRFH8325TRPBF	IRFI1010N	IRFM140
IRFH6200TRPBF	IRFH8330TRPBF	IRFI1310N	IRFM150
IRFH7084	IRFH8334TRPBF	IRFI3306GPBF	IRFM9140
IRFH7085	IRFH8337TRPBF	IRFI3710	IRFML8244TRPBF
IRFH7107TRPBF	IRFHM3911	IRFI4227	IRFN054
IRFH7185TRPBF	IRFHM4226TRPBF	IRFI4228PBF	IRFP044N
IRFH7188	IRFHM4231TRPBF	IRFI4321	IRFP048N
IRFH7191	IRFHM4234TRPBF	IRFI4410ZPBF	IRFP054N
IRFH7194	IRFHM792TRPBF	IRFI4510G	IRFP064
IRFH7440	IRFHM8228	IRFI520N	IRFP064N
IRFH7446	IRFHM8235TRPBF	IRFI5210	IRFP140N

Multisim 14.1 Education Components

IRFP150N	IRFP9140N	IRFR3518	IRFS3004-7PPBF
IRFP2410	IRFPG40	IRFR3607	IRFS3004PBF
IRFP244	IRFPS3810	IRFR3704ZPBF	IRFS3004TRL7PP
IRFP250	IRFPS3815	IRFR3704ZTRLPBF	IRFS3004TRLPBF
IRFP250N	IRFR024N	IRFR3704ZTRPBF	IRFS3006-7PPBF
IRFP260	IRFR1010Z	IRFR3707Z	IRFS3006TRL7PP
IRFP260N	IRFR1018E	IRFR3708	IRFS3107-7PPBF
IRFP264	IRFR110	IRFR3710Z	IRFS3107TRL7PP
IRFP2907ZPBF	IRFR1205	IRFR3711Z	IRFS31N20D
IRFP3006PBF	IRFR120N	IRFR3910	IRFS3206PBF
IRFP3703	IRFR120ZPBF	IRFR4104	IRFS3206TRRPBF
IRFP3710	IRFR120ZTRPBF	IRFR4105	IRFS3207
IRFP4127	IRFR13N20D	IRFR4105ZPBF	IRFS3207ZPBF
IRFP4332PBF	IRFR18N15D	IRFR4105ZTRPBF	IRFS3306PBF
IRFP4368PBF	IRFR220N	IRFR48ZPBF	IRFS3306TRLPBF
IRFP4468PBF	IRFR2307ZPBF	IRFR48ZTRLPBF	IRFS3307ZPBF
IRFP4568PBF	IRFR2307ZTRLPBF	IRFR48ZTRPBF	IRFS3307ZTRLPBF
IRFP4668PBF	IRFR2405	IRFR7446	IRFS3307ZTRRPBF
IRFP4768PBF	IRFR2407	IRFR7540	IRFS38N20D
IRFP5210	IRFR24N15D	IRFR7546	IRFS4010-7PPBF
IRFP7430PBF	IRFR2607ZPBF	IRFR7746	IRFS4010PBF
IRFP7530PBF	IRFR2607ZTRPBF	IRFR825PBF	IRFS4010TRL7PP
IRFP7537PBF	IRFR3303	IRFR825TRPBF	IRFS4010TRLPBF
IRFP7718	IRFR3410	IRFR8314	IRFS4010TRRPBF
IRFP90N20D	IRFR3504Z	IRFR9120N	IRFS4115PBF

Multisim 14.1 Education Components

IRFS4115TRLPBF	IRFS7534TRLPBF	IRFSL7540PBF	IRFZ46N
IRFS4127PBF	IRFS7537PBF	IRFSL7730	IRFZ46NS
IRFS4127TRLPBF	IRFS7537TRLPBF	IRFSL7734	IRFZ46ZS
IRFS4227PBF	IRFS7540PBF	IRFSL7787	IRFZ48N
IRFS4227TRLPBF	IRFS7540TRLPBF	IRFU110	IRFZ48NS
IRFS4321-7PPBF	IRFS7730-7P	IRFU1205	IRFZ48ZSPBF
IRFS4321TRL7PP	IRFS7734-7P	IRFU120N	IRG4BC10KDPBF
IRFS4410	IRFS7762	IRFU220N	IRG4BC10U
IRFS4410Z	IRFS7787	IRFU2605	IRG4BC10UD
IRFS4610	IRFSL3004PBF	IRFU3410	IRG4BC10UDPBF
IRFS52N15D	IRFSL3107	IRFU3710ZPBF	IRG4BC15UD
IRFS7430-7PPBF	IRFSL3206	IRFU3910	IRG4BC15UDPBF
IRFS7430PBF	IRFSL3207Z	IRFU4105	IRG4BC20FDPBF
IRFS7430TRL7PP	IRFSL3306	IRFU4105ZPBF	IRG4BC20SDPBF
IRFS7430TRLPBF	IRFSL3607	IRFU48ZPBF	IRG4BC20SD-SPBF
IRFS7434-7PPBF	IRFSL3806	IRFU7546	IRG4BC20U
IRFS7434PBF	IRFSL38N20D	IRFU7746	IRG4BC20UDPBF
IRFS7434TRL7PP	IRFSL4115PBF	IRFU9024N	IRG4BC20UPBF
IRFS7434TRLPBF	IRFSL4410Z	IRFZ24N	IRG4BC30FPBF
IRFS7440	IRFSL7430PBF	IRFZ24NS	IRG4BC30KDPBF
IRFS7530-7P	IRFSL7437	IRFZ34N	IRG4BC30UDPBF
IRFS7530PBF	IRFSL7440	IRFZ34NS	IRG4BC30UPBF
IRFS7530TRLPBF	IRFSL7530PBF	IRFZ44N	IRG4BC40S
IRFS7534-7P	IRFSL7534PBF	IRFZ44NS	IRG4BC40SPBF
IRFS7534PBF	IRFSL7537PBF	IRFZ44ZL	IRG4BC40U

Multisim 14.1 Education Components

IRG4BC40UPBF	IRG4PC50WPBF	IRG7PSH73K10PBF	IRGP4063D-EPBF
IRG4BC40W	IRG4PF50WPBF	IRGB15B60KDPBF	IRGP4063DPBF
IRG4BC40WPBF	IRG4PH20KPBF	IRGB20B60PD1PBF	IRGP4068D-EPBF
IRG4MC30F	IRG4PH50SPBF	IRGB30B60KPBF	IRGP4068DPBF
IRG4MC40U	IRG4PH50UDPBF	IRGB4045DPBF	IRGP50B60PD1PBF
IRG4MC50F	IRG4PH50UPBF	IRGB4059DPBF	IRGPC20F
IRG4MC50U	IRG4PSC71KDPBF	IRGB4060DPBF	IRGPC20U
IRG4PC30KDPBF	IRG4PSC71KPBF	IRGB4061DPBF	IRGPC40K
IRG4PC30KPBF	IRG4PSC71UPBF	IRGB4062DPBF	IRGPC40UD2
IRG4PC30U	IRG4RC10K	IRGB4B60KD1PBF	IRGPC50K
IRG4PC30UDPBF	IRG4RC10KD	IRGB5B120KDPBF	IRGPC50M
IRG4PC30UPBF	IRG4RC10U	IRGB8B60KPBF	IRGPH40K
IRG4PC40FPBF	IRG4RC10UD	IRGBC20F	IRGPH50K
IRG4PC40SPBF	IRG4RC10UDPBF	IRGBC20K	IRGPH50M
IRG4PC40UD-EPBF	IRG4RC10UDTRLP	IRGBC20S	IRGPS40B120UDP
IRG4PC40UDPBF	IRG4RC10UDTRP	IRGBC20U	IRGPS60B120KDP
IRG4PC40UPBF	IRG4RC10UDTRRP	IRGBC30F	IRGS15B60KDPBF
IRG4PC50FD-EPBF	IRG4RC10UTRPBF	IRGBC30K	IRGS30B60KPBF
IRG4PC50FDPBF	IRG4RC20FPBF	IRGBC30UD2	IRGS4B60KD1PBF
IRG4PC50KDPBF	IRG4RC20FTRLPBF	IRGLC60KD1	IRGS8B60KPBF
IRG4PC50KPBF	IRG4RC20FTRPBF	IRGP20B120UD-EP	IRGS8B60KTRLPBF
IRG4PC50SPBF	IRG7PH46UD-EP	IRGP30B120KD-EP	IRGSL15B60KDPBF
IRG4PC50UD-EPBF	IRG7PH46UDPBF	IRGP30B60KD-EP	IRGSL30B60KPBF
IRG4PC50UDPBF	IRG7PH46U-EP	IRGP4062D-EPBF	IRGSL4B60KD1PBF
IRG4PC50UPBF	IRG7PH46UPBF	IRGP4062DPBF	IRL1404ZPBF

Multisim 14.1 Education Components

IRL2203	IRL6297SDTRPBF	IRLI3303	IRLMS6702
IRL2203NS	IRL6342PBF	IRLI3705N	IRLMS6802
IRL2203S	IRL6342TRPBF	IRLI3803	IRLP150
IRL2505	IRL7833SPBF	IRLI530N	IRLP2203
IRL2505S	IRL7833STRLPBF	IRLIB9343	IRLP2505
IRL2703	IRL8113PBF	IRLIZ24N	IRLP3705
IRL2703S	IRL8113SPBF	IRLIZ34N	IRLP3803
IRL2910	IRL8113STRLPBF	IRLIZ44N	IRLR024N
IRL2910S	IRLB3034PBF	IRLL3303	IRLR2703
IRL3103	IRLB3036PBF	IRLML0030TRPBF	IRLR2705
IRL3103S	IRLB8748PBF	IRLML0040TRPBF	IRLR2905
IRL3303	IRLH5034TRPBF	IRLML0060TRPBF	IRLR2905ZPBF
IRL3303S	IRLH5036TRPBF	IRLML0100TRPBF	IRLR2905ZTRLPBF
IRL3705	IRLHM620TRPBF	IRLML2030TRPBF	IRLR2905ZTRPBF
IRL3705N	IRLHS2242TRPBF	IRLML2060TRPBF	IRLR3103
IRL3705NS	IRLHS6242TRPBF	IRLML2244TRPBF	IRLR3110ZPBF
IRL3713	IRLHS6276TRPBF	IRLML6244TRPBF	IRLR3110ZTRLPBF
IRL3803	IRLHS6342TRPBF	IRLML6246TRPBF	IRLR3110ZTRPBF
IRL3803S	IRLHS6376TRPBF	IRLML6346TRPBF	IRLR3110ZTRRPBF
IRL40B209	IRLI2203G	IRLML9301TRPBF	IRLR3303
IRL530N	IRLI2203N	IRLML9303TRPBF	IRLR3636PBF
IRL530NS	IRLI2505	IRLMS1503	IRLR3636TRLPBF
IRL540	IRLI2703	IRLMS1902	IRLR3636TRPBF
IRL540NS	IRLI2910	IRLMS2002	IRLR3705ZPBF
IRL6283MTRPBF	IRLI3103	IRLMS5703	IRLR3705ZTRPBF

Multisim 14.1 Education Components

IRLR3717PBF	IRLTS2242TRPBF	J177	J410
IRLR3717TRPBF	IRLU024N	J210	J411
IRLR3717TRRPBF	IRLU2703	J211	J412
IRLR3915	IRLU2705	J212	JAN2N2907A
IRLR6225PBF	IRLU2905	J2N5902	JAN2N3700
IRLR6225TRPBF	IRLU2905ZPBF	J2N5904	JAN2N4029
IRLR7807ZPBF	IRLU3103	J2N5905	JAN2N4033
IRLR7807ZTRPBF	IRLU3110ZPBF	J2N5906	JANTX2N2907A
IRLR8103V	IRLU3303	J2N5907	JANTX2N3700
IRLR8256PBF	IRLU3636PBF	J2N5908	JANTX2N4029
IRLR8256TRPBF	IRLU3705ZPBF	J2N5909	JANTX2N4033
IRLR8726PBF	IRLU8743PBF	J2N5911	JANTXV2N2907A
IRLR8726TRLPBF	IRLZ34N	J2N5912	JANTXV2N3700
IRLR8726TRPBF	IRLZ34NS	J2N6483	JANTXV2N4029
IRLR8729PBF	IRLZ44N	J2N6484	JANTXV2N4033
IRLR8729TRLPBF	IRLZ44NS	J2N6485	JFET_N
IRLR8729TRPBF	J108	J308	JFET_P
IRLR8743PBF	J109	J309	JK_FF
IRLR8743TRLPBF	J110	J310	JK_FF_NEGSR
IRLR8743TRPBF	J111	J401	KT88
IRLS4030-7PPBF	J112	J402	L1
IRLS4030PBF	J113	J403	L2
IRLS4030TRL7PP	J174	J404	L2081
IRLS4030TRLPBF	J175	J405	L2082
IRLSL4030PBF	J176	J406	L2083

Multisim 14.1 Education Components

L88008	LCD_DISPLAY_24x2	LF147J	LF353H
L88012	LCD_DISPLAY_30x2	LF147J/883	LF353M
L88016	LCD_DISPLAY_32x2	LF155AH	LF353N
LA_CARRY_GEN	LCD_DISPLAY_40x2	LF155AH/883	LF353P
LA_CARRY_GEN	LCD_DISPLAY_4DIGI T	LF155H	LF355AH
LAMP	LD102A	LF155H/883	LF355BM
LAMP_VIRTUAL	LD103A	LF156AH	LF355BN
LATCH_D	LD106	LF156AH/883	LF355H
LATCH_D2	LED	LF156H	LF355M
LATCH_D4_SR_OE	LED_blue	LF156H/883	LF355N
LATCH_SR	LED_BLUE_RATED	LF157AH/883	LF356AH
LATTICE- ispDOWNLOAD- HDR	LED_green	LF157H/883	LF356BM
LATTICE- ispDOWNLOAD- USB-HDR	LED_GREEN_RATED	LF255H	LF356BN
	LED_ir	LF256H	LF356H
	LED_orange	LF257H	LF356M
LC03-6R2G	LED_red	LF347BD	LF356M/NOPB
LCD_DISPLAY_08x1	LED_RED_RATED	LF347BN	LF356N
LCD_DISPLAY_08x2	LED_yellow	LF347D	LF356N/NOPB
LCD_DISPLAY_10x2	LED_YELLOW_RATE D	LF347M	LF357AH
LCD_DISPLAY_16x1		LF347N	LF357BN
LCD_DISPLAY_16x2	Led1_Red	LF351D	LF357H
LCD_DISPLAY_16x4	Led2_Yellow	LF351M	LF357M
LCD_DISPLAY_20x2	Led3_Green	LF351N	LF357N
LCD_DISPLAY_20x4	LF13741H	LF351P	LF400
	LF147D/883	LF353D	LF411ACH

Multisim 14.1 Education Components

LF411ACN	LF441CH	LH0004CH	LH0101AK-MIL
LF411AMH	LF441CJ	LH0004H	LH0101CK
LF411CD	LF441CM	LH0004H-MIL	LH0101K
LF411CH	LF441CN	LH0021CK	LH0101K-MIL
LF411CJG	LF441MH/883	LH0021K	LH1041G
LF411CN	LF442ACN	LH0022CD	LH4161
LF411CP	LF442AMH	LH0022CH	LH4162
LF411ID	LF442CD	LH0024CH	LHV870LC/NOPB
LF411IP	LF442CH	LH0024H	LIMIT_NC
LF411MH	LF442CJ	LH0024H-MIL	LIMIT_NO
LF411MH/883	LF442CM	LH0032CG	LINKSYS-WRT54G-HD
LF411MWG/883	LF442CN	LH0032G	LM101AD
LF412ACH	LF442MH	LH0032G/883	LM101AD/883
LF412ACN	LF442MH/883	LH0041CG	LM101AF
LF412AMH	LF444ACN	LH0041CJ	LM101AF/883
LF412CD	LF444AMD	LH0041G	LM101AFK
LF412CH	LF444CD	LH0042CH	LM101AFK/883
LF412CJG	LF444CJ	LH0042H	LM101AH
LF412CN	LF444CM	LH0042H-MIL	LM101AH/883
LF412CP	LF444CN	LH0062CD	LM101AJ
LF412MH	LF444MD/883	LH0062CH	LM101AJ/883
LF412MH/883	LF451CM	LH0062D	LM101AJ-14
LF412MJ/883	LF453CM	LH0062H	LM101AJ-14/883
LF441AMH	LH0003CH	LH0101ACK	LM101AJ8
LF441CD	LH0003H	LH0101AK	

Multisim 14.1 Education Components

LM101AJG	LM1084IT- 3.3/NOPB	LM108AL	LM10CWM
LM101AJG/883		LM108AP	LM10H
LM101AP	LM1084IT- 5.0/NOPB	LM108D	LM10H/883
LM101AU	LM1084IT- ADJ/NOPB	LM108D/883	LM1117DT- 1.8/NOPB
LM101AU/883		LM108H	LM1117DT- 2.5/NOPB
LM101AW	LM1085IS-12/NOPB	LM108H/883	
LM101AW/883	LM1085IS- 3.3/NOPB	LM108J	LM1117DT- 3.3/NOPB
LM101D	LM1085IS- 5.0/NOPB	LM108J/883	LM1117DT- 5.0/NOPB
LM101F	LM1085IS- ADJ/NOPB	LM108J8	LM1117DTX- ADJ/NOPB
LM101F/883		LM108J-8	
LM101H	LM1085IT-12/NOPB	LM108J8/883	LM1117IDTX- ADJ/NOPB
LM101H/883	LM1085IT- 3.3/NOPB	LM108J-8/883	
LM101J-14	LM1085IT- 5.0/NOPB	LM108JG	LM1117ILD- ADJ/NOPB
LM101J-14/883		LM108JG/883	
LM107J	LM1085IT- ADJ/NOPB	LM108L	LM1117IMP- 3.3/NOPB
LM107JG	LM108AD	LM108P	LM1117IMP- 5.0/NOPB
LM107JG/883	LM108AH	LM10BH	
LM107U	LM108AH/883	LM10BLH	LM1117IMPX- ADJ/NOPB
LM107W	LM108AJ	LM10CH	
LM107W/883	LM108AJ/883	LM10CLH	LM1117LD- 1.8/NOPB
LM1084IS- 3.3/NOPB	LM108AJ-8	LM10CLN	LM1117LD- 2.5/NOPB
LM1084IS- 5.0/NOPB	LM108AJ-8/883	LM10CLN8	
LM1084IS- ADJ/NOPB	LM108AJG	LM10CLWM	LM1117LD- 3.3/NOPB
		LM10CN	
		LM10CN8	

Multisim 14.1 Education Components

LM1117LDX- ADJ/NOPB	LM117HVKSTL/883	LM124AW/883	LM144H/883
	LM118D	LM124AWG/883	LM146J
LM1117MP- 1.8/NOPB	LM118FK	LM124D	LM146J/883
LM1117MP- 2.5/NOPB	LM118H	LM124E	LM149J
	LM118H/883	LM124E/883	LM149J/883
LM1117MPX- ADJ/NOPB	LM118J	LM124FK	LM158AD
	LM118J/883	LM124J	LM158AFK
LM1117SX- 3.3/NOPB	LM118J8	LM124J/883	LM158AH
LM1117SX- 5.0/NOPB	LM118J-8	LM124N	LM158AH/883
	LM118J8/883	LM124W	LM158AJ
LM1117SX- ADJ/NOPB	LM118J-8/883	LM124W/883	LM158AJG
LM1117T-2.5/NOPB	LM118JG	LM12CLK	LM158AN
LM1117T-3.3/NOPB	LM118L	LM12LK	LM158AP
LM1117T-5.0/NOPB	LM118P	LM13600AN	LM158AWG/883
	LM11CH	LM13600M	LM158D
	LM11CLH	LM13600N	LM158FK
LM111E	LM11CLN	LM13700AN	LM158H
LM111E/883	LM11H	LM13700M	LM158J
LM111H	LM124AD	LM13700N	LM158JG
LM111J-14	LM124AE	LM139AJ	LM158N
LM111J-8	LM124AE/883	LM139AW	LM158P
LM111W	LM124AFK	LM139E	LM160H
LM112H	LM124AJ	LM139J	LM160J
LM112H/883	LM124AJ/883	LM139W	LM160J-14
LM117HVH	LM124AN	LM144H	LM1877M-9

Multisim 14.1 Education Components

LM1877N-9	LM21212MH-1/NOPB	LM224DTBR2G	LM22672-ADJ
LM20123		LM224J	LM22672MR-5.0/NOPB
LM20123MH/NOPB	LM21212MH-2/NOPB	LM224N	LM22672MR-ADJ/NOPB
LM202H	LM21215	LM224NG	
LM207D	LM21215MH/NOPB	LM224P	LM22672QMR-ADJ/NOPB
LM207H	LM212H	LM22670-5.0	
LM207J	LM216AD	LM22670-ADJ	LM22673-5.0
LM207P	LM216AF	LM22670MR-5.0/NOPB	LM22673-ADJ
LM208AD	LM216AH	LM22670MR-ADJ/NOPB	LM22673MR-5.0/NOPB
LM208AH	LM216D		LM22673MR-ADJ/NOPB
LM208AJ	LM216F	LM22670QMR-ADJ/NOPB	
LM208AJ-8	LM216H	LM22670QTJ-ADJ/NOPB	LM22673TJ-5.0/NOPB
LM208AN	LM218D		LM22673TJ-ADJ/NOPB
LM208AP	LM218H	LM22670TJ-5.0/NOPB	
LM208D	LM218JG		LM22674-5.0
LM208H	LM218P	LM22670TJ-ADJ/NOPB	LM22674-ADJ
LM208J	LM221H		LM22674MR-5.0/NOPB
LM208J-8	LM224AD	LM22671-5.0	
LM208N	LM224AJ	LM22671-ADJ	LM22674MR-ADJ/NOPB
LM208P	LM224AN	LM22671MR-5.0/NOPB	LM22674QMR-ADJ/NOPB
LM211H	LM224AP	LM22671MR-ADJ/NOPB	
LM211J-8	LM224D		LM22675-5.0
LM211M	LM224DG	LM22671QMR-ADJ/NOPB	LM22675-ADJ
LM21212-1	LM224DR2G		LM22675MR-5.0/NOPB
LM21212-2	LM224DTBG	LM22672-5.0	

Multisim 14.1 Education Components

LM22675MR- ADJ/NOPB	LM22678TJ- 5.0/NOPB	LM25019SD/NOPB	LM258JG
LM22675QMR- ADJ/NOPB	LM22678TJ- ADJ/NOPB	LM25088-1	LM258N
LM22676-5.0	LM22679-5.0	LM25115MT/NOPB	LM258NG
LM22676-ADJ	LM22679-ADJ	LM25115SD/NOPB	LM258P
LM22676MR- 5.0/NOPB	LM22679TJ- 5.0/NOPB	LM25116	LM2592HVS- ADJ/NOPB
LM22676MR- ADJ/NOPB	LM22679TJ- ADJ/NOPB	LM25116MH/NOPB	LM2592HVT- ADJ/NOPB
LM22676QMR- ADJ/NOPB	LM22680-ADJ	LM25117	LM2594HVM- ADJ/NOPB
LM22676QTJ- ADJ/NOPB	LM22680MR- ADJ/NOPB	LM25119PSQ/NOP B	LM2594HVN- ADJ/NOPB
LM22676TJ- 5.0/NOPB	LM22680QMR- ADJ/NOPB	LM25574	LM2594M- ADJ/NOPB
LM22676TJ- ADJ/NOPB	LM239AJ	LM25574MT/NOPB	LM2594N- ADJ/NOPB
LM22677-5.0	LM239DG	LM25575	LM2594N- ADJ/NOPB
LM22677-ADJ	LM239DR2G	LM25575MH/NOPB	LM2596S-3.3/NOPB
LM22677QTJ- ADJ/NOPB	LM239DTBR2G	LM25576MH/NOPB	LM2596S-5.0/NOPB
LM22677TJ- 5.0/NOPB	LM239J	LM258AD	LM2596SX- 12/NOPB
LM22677TJ- ADJ/NOPB	LM239NG	LM258AH	LM2596T-12/LF03
LM22678-5.0	LM246J	LM258AJG	LM2596T-12/NOPB
LM22678-ADJ	LM25017MR/NOPB	LM258AN	LM2596T-3.3/LF03
LM22678QJTJ- ADJ/NOPB	LM25017SD/NOPB	LM258AP	LM2596T-3.3/NOPB
	LM25018MR/NOPB	LM258D	LM2596T-5.0/LF03
	LM25018SD/NOPB	LM258DG	LM2596T-5.0/NOPB
	LM25019MR/NOPB	LM258DMR2G	LM26001
		LM258DR2G	LM26001B
		LM258H	

Multisim 14.1 Education Components

LM26003	LM2679T- ADJ/NOPB	LM2830XMF/NOPB	LM2842XMK- ADJL/NOPB
LM26420XMH/NOP B	LM27313XMF/NOP B	LM2830ZMF/NOPB	LM2842XQMK/NOP B
LM26420XSQ/NOP B	LM2731XMF/NOPB	LM2831XMF/NOPB	LM2842Y
LM26420YMH/NOP B	LM2731YMF/NOPB	LM2831XSD/NOPB	LM2842YMK- ADJL/NOPB
LM26420YSQ/NOP B	LM27341MY/NOPB	LM2831YMF/NOPB	LM2842YQMK/NOP B
LM2673S- ADJ/NOPB	LM27341SD/NOPB	LM2831YSD/NOPB	LM2852X
LM2673SD- ADJ/NOPB	LM2734X	LM2831ZMF/NOPB	LM2852XMXA- 0.8/NOPB
LM2673T- ADJ/NOPB	LM2734XMK/NOPB	LM2831ZSD/NOPB	LM2852Y
LM2675LD- ADJ/NOPB	LM2734Y	LM2832XMY/NOPB	LM2852YMXA- 0.8/NOPB
LM2675M- ADJ/NOPB	LM2734YMK/NOPB	LM2832XSD/NOPB	LM2853
LM2675N- ADJ/NOPB	LM2735XMF/NOPB	LM2832YMY/NOPB	LM2853MH- 3.0/NOPB
LM2678-3.3	LM2735XMY/NOPB	LM2832YSD/NOPB	LM2854-1000
LM2678S-3.3/NOPB	LM2735XSD/NOPB	LM2832ZMY/NOPB	LM2854-500
LM2678SD- 3.3/NOPB	LM2735Y	LM2832ZSD/NOPB	LM2854MH- 1000/NOPB
LM2678T-3.3/NOPB	LM2735YMF/NOPB	LM2841X	LM2854MH- 500/NOPB
LM2679S- ADJ/NOPB	LM2735YMY/NOPB	LM2841XMK- ADJL/NOPB	LM2878P
LM2679SD- ADJ/NOPB	LM2735YSD/NOPB	LM2841XQMK/NOP B	LM2900N
	LM27402	LM2841Y	LM2901DG
	LM27402MH/NOPB	LM2841YMK- ADJL/NOPB	LM2901DR2G
	LM27402SQ/NOPB	LM2841YQMK/NOP B	
	LM27403SQ/NOPB	LM2842X	
	LM2743		
	LM2743MTC/NOPB		
	LM2830X		

Multisim 14.1 Education Components

LM2901DTBR2G	LM2904ADMR2G	LM293DMR2G	LM2940T-9.0/NOPB
LM2901NG	LM2904AN	LM293DR2G	LM2941LD/NOPB
LM2901VDG	LM2904ANG	LM2940IMP-10/NOPB	LM2941S/NOPB
LM2901VDR2G	LM2904D	LM2940IMP-12/NOPB	LM2941T/LF03
LM2901VDTBR2G	LM2904DG	LM2940IMP-15/NOPB	LM2941T/NOPB
LM2901VNG	LM2904DMR2G	LM2940IMP-5.0/NOPB	LM3017LE/NOPB
LM2902DG	LM2904DR2G	LM2940IMP-9.0/NOPB	LM301AD
LM2902DR2G	LM2904ITP	LM2940IMPX-8.0/NOPB	LM301AJ8
LM2902DTBG	LM2904M	LM2940LD-12/NOPB	LM301AP
LM2902DTBR2G	LM2904N	LM2940LD-5.0/NOPB	LM3046M
LM2902M	LM2904NG	LM2940S-10/NOPB	LM307D
LM2902MT	LM2904P	LM2940S-12/NOPB	LM307N
LM2902N	LM2904PW	LM2940S-5.0/NOPB	LM307P
LM2902NG	LM2904QD	LM2940S-8.0/NOPB	LM308AD
LM2902VD	LM2904QP	LM2940S-9.0/NOPB	LM308AH
LM2902VDG	LM2904VD	LM2940T-10.0/NOPB	LM308AJ
LM2902VDR2G	LM2904VDG	LM2940T-12.0/NOPB	LM308AJ-8
LM2902VDTBG	LM2904VDMR2G	LM2940T-5.0/NOPB	LM308AN
LM2902VDTBR2G	LM2904VDR2G	LM2940T-8.0/NOPB	LM308AN8
LM2902VN	LM2904VN	LM2940T-9.0/NOPB	LM308D
LM2903DG	LM2904VNG	LM2940T-10.0/NOPB	LM308H
LM2903DMR2G	LM2924M	LM2940T-12.0/NOPB	LM308J
LM2903DR2	LM2924N	LM2940T-5.0/NOPB	LM308J-8
LM2903DR2G	LM293D	LM2940T-8.0/NOPB	LM308M
LM2903NG	LM293DG		LM308N

Multisim 14.1 Education Components

LM308N8	LM324AJ	LM339DG	LM34919TL/NOPB
LM3100MH/NOPB	LM324AM	LM339DR2G	LM34925MR/NOPB
LM3102MH/NOPB	LM324AN	LM339DTBR2G	LM34925SD/NOPB
LM3102TL-1/NOPB	LM324ANG	LM339J	LM34926MR/NOPB
LM311H	LM324AP	LM339M	LM34926SD/NOPB
LM311M	LM324APWLE	LM339N	LM34927MR/NOPB
LM311N	LM324D	LM339NG	LM34927SD/NOPB
LM311N-14	LM324DBLE	LM344H	LM358AD
LM312H	LM324DG	LM346J	LM358ADR2G
LM318D	LM324DR2G	LM346M	LM358AH
LM318H	LM324DTBG	LM346N	LM358AJG
LM318J8	LM324DTBR2G	LM3481	LM358AM
LM318J-8	LM324J	LM3481MM/NOPB	LM358AN
LM318M	LM324M	LM3485MM/NOPB	LM358AP
LM318N	LM324MT	LM3489MM/NOPB	LM358BP
LM318N8	LM324N	LM348D	LM358D
LM318P	LM324NG	LM348N	LM358DB
LM318S8	LM324P	LM348PW	LM358DG
LM321AH	LM324PWLE	LM34910CSD/NOPB	LM358DMR2G
LM321H	LM324x2DBLE	LM34910SD/NOPB	LM358DR2G
LM324AD	LM3301N	LM34914SD/NOPB	LM358H
LM324ADG	LM3302N	LM34917ATL/NOPB	LM358J
LM324ADR2G	LM339AJ	LM34919CQSD/NO PB	LM358JG
LM324ADTBG	LM339AM	LM34919CQTL/NOP B	LM358M
LM324ADTBR2G	LM339AN		LM358N

Multisim 14.1 Education Components

LM358NG	LM4040AIM3- 10.0/NOPB	LM4040BIM3- 5.0/NOPB	LM4040CIM3- 8.2/NOPB
LM358P			
LM358PW	LM4040AIM3- 2.0/NOPB	LM4040BIM3- 8.2/NOPB	LM4040CIM7- 2.0/NOPB
LM358TP	LM4040AIM3- 2.5/NOPB	LM4040BIM7- 2.0/NOPB	LM4040CIM7- 2.5/NOPB
LM359J			
LM359M	LM4040AIM3- 3.0/NOPB	LM4040BIM7- 2.5/NOPB	LM4040CIZ- 10.0/NOPB
LM359N	LM4040AIM3- 4.1/NOPB	LM4040BIM7- 5.0/NOPB	LM4040CIZ- 2.5/LFT8
LM3875TF/NOPB			
LM3900D	LM4040AIM3- 5.0/NOPB	LM4040BIZ- 10.0/NOPB	LM4040CIZ- 4.1/NOPB
LM3900M			
LM3900N	LM4040AIZ- 10.0/NOPB	LM4040BIZ- 2.5/NOPB	LM4040CIZ- 5.0/NOPB
LM393DG	LM4040AIZ- 2.5/NOPB	LM4040BIZ- 4.1/NOPB	LM4040DEM3- 2.0/NOPB
LM393DMR2G			
LM393DR2G	LM4040AIZ- 4.1/NOPB	LM4040BIZ- 5.0/NOPB	LM4040DEM3- 2.5/NOPB
LM393NG	LM4040AIZ- 5.0/NOPB	LM4040CEM3- 2.5/NOPB	LM4040DEM3- 3.0/NOPB
LM4030AMF- 2.5/NOPB	LM4040BIM3- 10.0/NOPB	LM4040CEM3- 3.0/NOPB	LM4040DEM3- 5.0/NOPB
LM4030AMF- 4.096/NOPB	LM4040BIM3- 2.0/NOPB	LM4040CEM3- 5.0/NOPB	LM4040DIM3- 10.0/NOPB
LM4030BMF- 2.5/NOPB	LM4040BIM3- 2.5/NOPB	LM4040CIM3- 10.0/NOPB	LM4040DIM3- 4.1/NOPB
LM4030BMF- 4.096/NOPB	LM4040BIM3- 3.0/NOPB	LM4040CIM3- 2.0/NOPB	LM4040DIM3- 8.2/NOPB
LM4030CMF- 2.5/NOPB	LM4040BIM3- 4.1/NOPB	LM4040CIM3- 4.1/NOPB	LM4040DIM7- 2.0/NOPB
LM4030CMF- 4.096/NOPB			

Multisim 14.1 Education Components

LM4040DIM7- 2.5/NOPB	LM4041CEM3- ADJ/NOPB	LM4050AEM3- 2.0/NOPB	LM4050CIM3X- 2.0/NOPB
LM4040DIM7- 5.0/NOPB	LM4041CIM7- 1.2/NOPB	LM4050AEM3- 2.5/NOPB	LM4051AIM3- 1.2/NOPB
LM4040DIZ- 10.0/NOPB	LM4041CIM7- ADJ/NOPB	LM4050AEM3- 5.0/NOPB	LM4051AIM3- ADJ/NOPB
LM4040DIZ- 2.5/NOPB	LM4041CIZ- 1.2/NOPB	LM4050AEM3- 8.2/NOPB	LM4250CH LM4250CM
LM4040DIZ- 4.1/NOPB	LM4041CIZ- ADJ/NOPB	LM4050AIM3- 4.1/NOPB	LM4250CN LM4250H
LM4040DIZ- 5.0/LFT1	LM4041DEM3- 1.2/NOPB	LM4050BEM3- 10/NOPB	LM4250J
LM4040EEM3- 2.5/NOPB	LM4041DEM3- ADJ/NOPB	LM4050BEM3- 2.5/NOPB	LM4250J-MIL LM43600PWP
LM4040EEM3- 3.0/NOPB	LM4041DIM7- 1.2/NOPB	LM4050BEM3- 4.1/NOPB	LM43601PWP
LM4040EIM7- 2.0/NOPB	LM4041DIM7- ADJ/NOPB	LM4050BEM3- 5.0/NOPB	LM43602PWP LM43603PWP
LM4041AIM3- 1.2/NOPB	LM4041DIZ- 1.2/NOPB	LM4050BEM3- 8.2/NOPB	LM4562HA LM4562MA
LM4041AIZ- 1.2/NOPB	LM4041DIZ- ADJ/LFT1	LM4050BIM3X- 2.0/NOPB	LM4562NA
LM4041BIM3- 1.2/NOPB	LM4041DIZ- ADJ/NOPB	LM4050CEM3- 2.5/NOPB	LM46000PWP LM46001PWP
LM4041BIM7- 1.2/NOPB	LM4041EEM3- 1.2/NOPB	LM4050CEM3- 5.0/NOPB	LM46002PWP
LM4041BIZ- 1.2/NOPB	LM4041EIM7- 1.2/NOPB	LM4050CIM3- 10/NOPB	LM4871LD LM4871M
LM4041CEM3- 1.2/NOPB	LM4050AEM3- 10/NOPB	LM4050CIM3- 4.1/NOPB	LM4871MM/NOPB LM4871MX

Multisim 14.1 Education Components

LM48860TL/NOPB	LM5085MM/NOPB	LM5116	LM5576MH/NOPB
LM4890M/NOPB	LM5085MY/NOPB	LM5116MH/NOPB	LM607ACH
LM4890MM/NOPB	LM5085SD/NOPB	LM5117PMH/NOPB	LM607ACN
LM5001MA/NOPB	LM5088	LM5117PSQ/NOPB	LM607AMH
LM5001SD/NOPB	LM5088MH- 2/NOPB	LM5119PSQ/NOPB	LM607BCH
LM5002MA/NOPB	LM5110-1M/NOPB	LM5121MH/NOPB	LM607BCN
LM5002SD/NOPB	LM5110-1SD/NOPB	LM5122MH/NOPB	LM607BMH
LM5008MM/NOPB	LM5110-2M/NOPB	LM5160DNTJ	LM607CH
LM5008SDC/NOPB	LM5110-2SD/NOPB	LM536023QPWPTQ 1	LM607CN
LM5009MM/NOPB	LM5110-3M/NOPB	LM536025QPWPTQ 1	LM6118E/883
LM5009SDC/NOPB	LM5110-3SD/NOPB	LM53602AQWPTQ 1	LM6118J/883
LM5010AMH/NOPB	LM5111-1M/NOPB	LM53602AQWPTQ 1	LM6118N
LM5010ASD/NOPB	LM5111- 1MY/NOPB	LM536033QPWPTQ 1	LM6132AIM
LM5017MR/NOPB	LM5111-2M/NOPB	LM536035QPWPTQ 1	LM6132AIM
LM5017SD/NOPB	LM5111- 2MY/NOPB	LM53603AQWPTQ 1	LM6132BIN
LM5018MR/NOPB	LM5111- 3MX/NOPB	LM555CM	LM6134AIM
LM5018SD/NOPB	LM5111-4M/NOPB	LM555CN	LM6134AIM
LM5019MR/NOPB	LM5111- 4MY/NOPB	LM556CM	LM6134BIN
LM5019SD/NOPB	LM5112MY/NOPB	LM556CN	LM6142AIM
LM5030MM/NOPB	LM5112SD/NOPB	LM5574	LM6142AMJ-MLS
LM5030SD/NOPB	LM5113SD/NOPB	LM5574MT/NOPB	LM6142AMJ-QML
LM5045MH/NOPB	LM5113TME/NOPB	LM5575MH/NOPB	LM6142BIM
LM5045SQ/NOPB			
LM5046MH/NOPB			
LM5046SQ/NOPB			

Multisim 14.1 Education Components

LM6142BIN	LM6165W/883	LM6265N	LM637BCH
LM6144AIM	LM6165WG/883	LM627ACH	LM637BMH
LM6144AIN	LM6171AIM	LM627AMH	LM637CH
LM6144BIM	LM6171BIM	LM627BCH	LM637CN
LM6144BIN	LM6171BIN	LM627BMH	LM709AH
LM6152ACM	LM6172AMJFQML	LM627CH	LM709CH
LM6152BCM	LM6172AMWGFQ ML	LM627CN	LM709CN
LM6161E/883	LM6172IM	LM6310IM	LM709CN-8
LM6161J	LM6172IN	LM6310IN	LM709H
LM6161J/883	LM6181IM	LM6311IM	LM710AMJ
LM6161W/883	LM6181IN	LM6311IN	LM710AMW
LM6161WG/883	LM6211MF	LM6313N	LM710CH
LM6162E/883	LM6218AN	LM6317IM	LM710CN
LM6162J/883	LM6218AWM	LM6317IN	LM710H
LM6162N	LM6218N	LM6361J	LM7121IM
LM6162W/883	LM6218WM	LM6361M	LM7121IM5
LM6162WG/883	LM6261J	LM6361N	LM7131ACM
LM6164E/883	LM6261M	LM6362M	LM7131ACM5
LM6164J	LM6261N	LM6362N	LM715CH
LM6164J/883	LM6262M	LM6364M	LM715CJ
LM6164W/883	LM6262N	LM6364N	LM715MH
LM6164WG/883	LM6264J	LM6365M	LM715MJ
LM6165E/883	LM6264N	LM6365N	LM7171AIM
LM6165J	LM6265J	LM637ACH	LM7171AIN
LM6165J/883		LM637AMH	LM7171AMJFQML

Multisim 14.1 Education Components

LM7171BIM	LM741CJ	LM7818CT	LMC6001AIH
LM7171BIN	LM741CM	LM7824CT	LMC6001AIN
LM723CN	LM741CN	LM7905CT	LMC6001BIH
LM723E	LM741EH	LM7909CT	LMC6001BIN
LM723H	LM741EN	LM7912CT	LMC6022IM
LM725AH	LM741H	LM7915CT	LMC6024IM
LM725AH/883	LM741H/883	LM7918CT	LMC6032IM
LM725CH	LM741J	LM7924CT	LMC6032IN
LM725CN	LM741J/883	LM809M3- 2.63/NOPB	LMC6034IM
LM725H	LM741J-14/883		LMC6035IBP
LM725H/883	LM741W/883	LM809M3- 2.93/NOPB	LMC6035IM
LM7301IM	LM747AH	LM809M3- 3.08/NOPB	LMC6035IMM
LM7301IM5	LM747AJ		LMC6035ITL
LM7321MA	LM748CH	LM809M3- 4.38/NOPB	LMC6036IM
LM7321MF	LM748CJ	LM809M3- 4.63/NOPB	LMC6036IMT
LM7322MA	LM748CN		LMC6041AIM
LM7322MM	LM748H	LM8261M5	LMC6041AIN
LM7332MA	LM759CH	LM8272MM	LMC6041IM
LM7332MM	LM759CP	LM833D	LMC6041IN
LM7341MF	LM759H/883	LM833DG	LMC6042AIM
LM7372IMA	LM759MH	LM833DR2G	LMC6042AIN
LM7372MR	LM7805CT	LM833NG	LMC6042IM
LM741AH/883	LM7809CT	LMC555CH	LMC6042IN
LM741AJ-14/883	LM7812CT	LMC555CM	LMC6044AIM
LM741CH	LM7815CT	LMC555CN	LMC6044AIN

Multisim 14.1 Education Components

LMC6044IM	LMC6082AIM	LMC6464BIM	LMC6494BEM
LMC6044IN	LMC6082AIN	LMC6464BIN	LMC6494BEN
LMC6061AIM	LMC6082AMN	LMC6464IM	LMC6572AIM
LMC6061AIN	LMC6082IM	LMC6464IN	LMC6572AIN
LMC6061AMJ/883	LMC6082IN	LMC6482AIM	LMC6572BIM
LMC6061AMN	LMC6084AIM	LMC6482AIN	LMC6572BIN
LMC6061IM	LMC6084AIN	LMC6482AMJ/883	LMC6574AIM
LMC6061IN	LMC6084AMN	LMC6482IM	LMC6574AIN
LMC6062AIM	LMC6084IM	LMC6482IMM	LMC6574BIM
LMC6062AIN	LMC6084IN	LMC6482IN	LMC6574BIN
LMC6062AMJ/883	LMC6442AIM	LMC6482MN	LMC6582AIM
LMC6062AMN	LMC6442IM	LMC6484AIM	LMC6582AIN
LMC6062IM	LMC6442IN	LMC6484AIN	LMC6582BIM
LMC6062IN	LMC6462AIM	LMC6484AMJ/883	LMC6582BIN
LMC6064AIM	LMC6462AIN	LMC6484AMWG/8 83	LMC6584AIM
LMC6064AIN	LMC6462AMN	LMC6484IM	LMC6584AIN
LMC6064AMJ/883	LMC6462BIM	LMC6484IN	LMC6584BIM
LMC6064AMN	LMC6462BIN	LMC6484MN	LMC6584BIN
LMC6064IM	LMC6462IM	LMC6492AEM	LMC660AIM
LMC6064IN	LMC6462IN	LMC6492AEN	LMC660AIN
LMC6081AIM	LMC6464AIM	LMC6492BEM	LMC660AMD
LMC6081AIN	LMC6464AIN	LMC6492BEN	LMC660AMJ/883
LMC6081AMN	LMC6464AMN	LMC6494AEM	LMC660CM
LMC6081IM	LMC6464AMWG- QML	LMC6494AEN	LMC660CN
LMC6081IN			LMC662AIM

Multisim 14.1 Education Components

LMC662AIN	LMC7101BIM5	LME49720MA	LMH6553SD
LMC662AMD	LMC7101BIN	LME49720NA	LMH6554LE
LMC662AMJ/883	LMC7111BIM5	LME49721MA/NOP B	LMH6555SQ
LMC662CM	LMC7211AIM	LME49740MA	LMH6559MA
LMC662CN	LMC7211AIM5	LME49740NA	LMH6559MF
LMC6681AIM	LMC7211BIM	LME49990MA/NOP B	LMH6601MG
LMC6681AIN	LMC7211BIM5		LMH6609MA
LMC6681BIM	LMC7215IM	LMH3401IRMSR	LMH6609MF
LMC6681BIN	LMC7215IM5	LMH5401IRMSR	LMH6611MK
LMC6682AIM	LMC7221AIM	LMH6321MR	LMH6612MA
LMC6682AIN	LMC7221AIM5	LMH6321TS	LMH6618MK
LMC6682BIM	LMC7221BIM	LMH6502MA	LMH6619MA
LMC6682BIN	LMC7221BIM5	LMH6502MT	LMH6622MA
LMC6684AIM	LMC7225IM5	LMH6503MA	LMH6622MM
LMC6684AIN	LMC8101BP	LMH6503MT	LMH6624J-QML
LMC6684BIM	LMC8101MM	LMH6505MA	LMH6624MA
LMC6684BIN	LMC8101TP	LMH6505MM	LMH6624MF
LMC6762AIM	LME49600TS/NOPB	LMH6521SQ/NOPB	LMH6628JFQML
LMC6762BIM	LME49710HA	LMH6550MA	LMH6628MA
LMC6772AIM	LME49710MA	LMH6550MM	LMH6628WGFQML
LMC6772AIMM	LME49710NA	LMH6551MA	LMH6629MF
LMC6772BIM	LME49713HA/NOP B	LMH6551MM	LMH6629SD
LMC6772BIN	LME49713MA/NOP B	LMH6552MA	LMH6639MA
LMC7101AIM5		LMH6552SD	LMH6639MF
LMC7101AIN	LME49720HA	LMH6553MR	LMH6642MA

Multisim 14.1 Education Components

LMH6642MF	LMH6672MA	LMH6739MQ	LMP7701MA
LMH6642MFXEP	LMH6672MR	LMP2011MA	LMP7701MF
LMH6643MA	LMH6702J-QML	LMP2011MF	LMP7702MA
LMH6643MAXEP	LMH6702MA	LMP2015MA	LMP7702MM
LMH6643MM	LMH6702MF	LMP2015MF	LMP7704MA
LMH6644MA	LMH6703MA	LMP2016MA	LMP7704MT
LMH6644MAXEP	LMH6703MF	LMP2016MM	LMP7707MF
LMH6644MT	LMH6704MA/NOPB	LMP2021MA	LMP7708MM
LMH6645MA	LMH6704MF/NOPB	LMP2021MF	LMP7709MT
LMH6645MA/NOPB	LMH6714J-QML	LMP2022MA	LMP7711MK
LMH6645MF	LMH6714MA	LMP2022MM	LMP7712MM
LMH6645MF/NOPB	LMH6714MF	LMP2231AMA	LMP7715MF
LMH6646MA	LMH6715JFQML	LMP2231AMF	LMP7716MM
LMH6646MM	LMH6715MA	LMP2231BMA	LMP7717MA
LMH6647MA	LMH6718MA	LMP2231BMF	LMP7717MF
LMH6647MF	LMH6720J-QML	LMP2232AMA	LMP7718MA
LMH6654MA/NOPB	LMH6720MA	LMP2232AMM	LMP7718MM
LMH6654MF/NOPB	LMH6720MF	LMP2232BMA	LMP7731MA
LMH6655MA	LMH6722J-QML	LMP2232BMM	LMP7731MF
LMH6655MM	LMH6722MA	LMP2234AMA	LMP7732MA
LMH6657MF	LMH6722MT	LMP2234AMT	LMP7732MM
LMH6657MG	LMH6723MA	LMP2234BMA	LMP8270MA
LMH6658MA/NOPB	LMH6723MF	LMP2234BMT	LMP8271MA
LMH6658MM/NOP B	LMH6733MQ	LMP7300MA	LMP8272MA
	LMH6738MQ	LMP7300MM	LMP8275MA

Multisim 14.1 Education Components

LMP8276MA	LMP8672MA/NOPB	LMR14203X	LMS1585ACT-1.5/NOPB
LMP8277MA	LMP8674MA/NOPB	LMR14203XMK/NO PB	LMS1585ACT-3.3/NOPB
LMP8278QMM/NO PB	LMR10510XMF/NO PB	LMR14206X	LMS1585AIS-1.5/NOPB
LMP8480MME-S/NOPB	LMR10510YMF/NO PB	LMR14206XMK/NO PB	LMS1585AIS-3.3/NOPB
LMP8480MM-T/NOPB	LMR10510YSD/NOPB	LMR16006XDDCR	LMS1587CS-1.5/NOPB
LMP8481MM-H/NOPB	LMR10515XMF/NO PB	LMR16006YDDCR	LMS1587CS-3.3/NOPB
LMP8481MM-S/NOPB	LMR10515XSD/NOPB	LMR24210TL/NOPB	LMS1587CS-ADJ/NOPB
LMP8481MM-T/NOPB	LMR10515YMF/NO PB	LMR24220TL/NOPB	LMS1587CT-3.3/NOPB
LMP8601MA	LMR10515YSD/NOPB	LMR61428XMM/NOPB	LMS1587CT-ADJ/NOPB
LMP8601QMA	LMR10520XSD/NOPB	LMR62014XMF/NO PB	LMS1587CT-3.3/NOPB
LMP8602MA	LMR10520YSD/NOPB	LMR62421X	LMS1587IT-1.5/NOPB
LMP8602MM	LMR12010X	LMR62421XMF/NO PB	LMV2011MA
LMP8602QMA	LMR12010XMK/NO PB	LMR62421XSD/NOPB	LMV2011MF
LMP8602QMM	LMR12010Y	LMR64010XMF/NO PB	LMV321M5
LMP8603MA	LMR12010YMK/NO PB	LMR70503TM/NOPB	LMV321M5/NOPB
LMP8603MM	LMR14006XDDCR	LMS1585ACS-1.5/NOPB	LMV321M7
LMP8603QMA	LMR14006YDDCR	LMS1585ACS-3.3/NOPB	LMV321M7/NOPB
LMP8603QMM	LMR14020SDDA	LMS1585ACSX-ADJ/NOPB	LMV324M
LMP8645HVMK			LMV324MT
LMP8645MK			LMV331M5
LMP8671MA/NOPB			

Multisim 14.1 Education Components

LMV331M7	LMV612MM/NOPB	LMV772QMM	LMV852MM
LMV339M	LMV614MA/NOPB	LMV774MT	LMV854MT
LMV339MT	LMV614MT/NOPB	LMV791MK	LMV861MG
LMV342MA	LMV641MA	LMV792MM	LMV862MM
LMV342MM	LMV641MG	LMV793MA	LMV881LE/NOPB
LMV358M	LMV651MG	LMV793MF	LMV931MF
LMV358MM	LMV652MM	LMV794MA	LMV931MG
LMV393M	LMV654MT	LMV794MM	LMV932MA
LMV393MM	LMV711M6	LMV796MF	LMV932MM
LMV431AIM5/NOP B	LMV716MM	LMV797MM	LMV934MA
LMV431AIMF/NOP B	LMV7219M5	LMV821M5	LMV934MT
	LMV7219M7	LMV821M7	LMV951MK
LMV431AIZ/LFT3	LMV721M5	LMV822M	LMV981BL
LMV431AIZ/NOPB	LMV721M7	LMV822MM	LMV981MF
LMV551MG	LMV7271MF	LMV824M	LMV981MG
LMV552MM	LMV7271MG	LMV824MT	LMV981TL
LMV554MT	LMV7275MF/NOPB	LMV831MG	LMX321AUK+
LMV601MG/NOPB	LMV7275MG/NOPB	LMV832MM	LMX321AXK+
LMV602MA/NOPB	LMV7291MG	LMV834MT	LMX324ASD+
LMV602MM/NOPB	LMV751M5	LMV841MG	LMX324AUD+
LMV604MA/NOPB	LMV761MA	LMV842MA	LMX358AKA+
LMV604MT/NOPB	LMV761MF	LMV842MM	LMX358ASA+
LMV611MF/NOPB	LMV771MG	LMV844MA	LMX358AUA+
LMV611MG/NOPB	LMV772MA	LMV844MT	LMZ10500SILR
LMV612MA/NOPB	LMV772MM	LMV851MG	LMZ10501

Multisim 14.1 Education Components

LMZ10501SILR	LMZ12008TZ/NOPB	LMZ21701SILR	LMZ31710RVQR
LMZ10503	LMZ12010	LMZ22003	LMZ34002RKGR
LMZ10503EXT	LMZ12010TZ/NOPB	LMZ22003TZ/NOPB	LMZ35003RKGR
LMZ10503EXTTZ/N OPB	LMZ13608	LMZ22005	LOG101AID
LMZ10503TZ- ADJ/NOPB	LMZ13608TZ/NOPB	LMZ22005TZ/NOPB	LOG102AID
LMZ10504	LMZ13610	LMZ22008	LOG104AID
LMZ10504TZ- ADJ/NOPB	LMZ13610TZ/NOPB	LMZ22008TZ/NOPB	LOG112AID
LMZ10505	LMZ14201EXTTZ/N OPB	LMZ22010	LOG114AIRGVR
LMZ10505EXT	LMZ14201HTZ/NOP B	LMZ22010TZ/NOPB	LOSSLESS_LINE_TYP E1
LMZ10505EXTTZ/N OPB	LMZ14201TZ- ADJ/NOPB	LMZ223603	LOSSLESS_LINE_TYP E2
LMZ10505TZ- ADJ/NOPB	LMZ14202EXTTZ/N OPB	LMZ223603TZ/NOPB	LOSSY_TRANSMISSI ON_LINE
LMZ12001EXTTZ/N OPB	LMZ14202HTZ/NOP B	LMZ223608	LP111JG
LMZ12001TZ- ADJ/NOPB	LMZ14202TZ- ADJ/NOPB	LMZ223608TZ/NOPB	LP124J
LMZ12002EXTTZ/N OPB	LMZ14203EXTTZ/N OPB	LMZ223610	LP211D
LMZ12002TZ- ADJ/NOPB	LMZ14203HTZ/NOP B	LMZ223610TZ/NOPB	LP211JG
LMZ12003EXTTZ/N OPB	LMZ14203TZ- ADJ/NOPB	LMZ30602RKGR	LP211P
LMZ12003TZ- ADJ/NOPB	LMZ20501SILR	LMZ30604RKGR	LP239D
LMZ12008	LMZ20502SILR	LMZ30606RKGR	LP239J
	LMZ21700SILR	LMZ31503RUQT	LP239N
		LMZ31506HRUQR	LP2901D
		LMZ31506RUQR	LP2901J
		LMZ31520RLGT	LP2901N
		LMZ31530RLGT	LP2902M
		LMZ31704RVQR	
		LMZ31707RVQR	

Multisim 14.1 Education Components

LP2902N	LP2989AIM- 2.5/NOPB	LP2992ILD- 1.8/NOPB	LP339N
LP2954AIM/NOPB			LP38502ASD- ADJ/NOPB
LP2985AIM5- 2.5/NOPB	LP2989AIM- 3.3/NOPB	LP2992ILD- 2.5/NOPB	LP38502ATJ- ADJ/NOPB
LP2985AIM5- 3.3/NOPB	LP2989AIM- 5.0/NOPB	LP2992ILD- 3.3/NOPB	LP38502SD- ADJ/NOPB
LP2985AIM5- 5.0/NOPB	LP2989AIMM- 2.5/NOPB	LP2992ILD- 5.0/NOPB	LP38502TJ- ADJ/NOPB
LP2985AITL- 3.3/NOPB	LP2989AIMM- 3.3/NOPB	LP2992ILDX- 1.5/NOPB	LP38502TS- ADJ/NOPB
LP2985AITP- 3.3/NOPB	LP2989AIMM- 5.0/NOPB	LP2992IM5- 1.5/NOPB	LP38690SD- 1.8/NOPB
LP2985AITP- 5.0/NOPB	LP2992AILD- 1.5/NOPB	LP2992IM5- 1.8/NOPB	LP38690SD- 2.5/NOPB
LP2985IM5- 2.5/NOPB	LP2992AILD- 1.8/NOPB	LP2992IM5- 2.5/NOPB	LP38690SD- 3.3/NOPB
LP2985IM5- 3.3/NOPB	LP2992AILD- 3.3/NOPB	LP2992IM5- 3.3/NOPB	LP38690SD- 5.0/NOPB
LP2985IM5- 5.0/NOPB	LP2992AILD- 5.0/NOPB	LP2992IM5- 5.0/NOPB	LP38690SD- ADJ/NOPB
LP2985ITP- 2.5/NOPB	LP2992AIM5- 1.5/NOPB	LP2998MA/NOPB	LP38691SD- 3.3/NOPB
LP2985ITP- 3.3/NOPB	LP2992AIM5- 1.8/NOPB	LP2998MR/NOPB	LP38691SD- ADJ/NOPB
LP2985ITP- 5.0/NOPB	LP2992AIM5- 2.5/NOPB	LP311M	LP38692MP- ADJ/NOPB
LP2989AILD- 3.3/NOPB	LP2992AIM5- 3.3/NOPB	LP311N	LP38692SD- ADJ/NOPB
LP2989AILD- 5.0/NOPB	LP2992AIM5- 5.0/NOPB	LP324M	LP38693MP- ADJ/NOPB
		LP324N	
		LP339D	
		LP339J	
		LP339M	

Multisim 14.1 Education Components

LP38693SD- ADJ/NOPB	LP5907UVE- 2.85/NOPB	LPV511MG	LT1006CH
		LPV521MG	LT1006CJ8
LP38798SD- ADJ/NOPB	LP5907UVE- 3.2/NOPB	LPV542DNXR	LT1006CN8
LP5900SD- 1.5/NOPB	LPC660AIM	LT1001	LT1006MH
	LPC660AIN	LT1001ACH	LT1006MJ8
LP5900SD- 2.8/NOPB	LPC660AMD	LT1001ACJ8	LT1006S8
LP5900SD- 3.3/NOPB	LPC660AMJ/883	LT1001ACN8	LT1007ACH
	LPC660IM	LT1001AMH/883	LT1007ACJ8
LP5900TL- 1.5/NOPB	LPC661AIM	LT1001AMJ8/883	LT1007ACN8
	LPC661AIN	LT1001CH	LT1007ACP
LP5900TL- 2.8/NOPB	LPC661AMN	LT1001CJ8	LT1007AMH
LP5900TL- 3.3/NOPB	LPC661IM	LT1001CN8	LT1007AMJ8
	LPC661IN	LT1001CS8	LT1007AMJG
LP5900XRX- 2.8/NOPB	LPC662AIM	LT1001MH	LT1007AML
	LPC662AIN	LT1001MJ8	LT1007AMP
LP5907MFX- 1.5/NOPB	LPC662AMD	LT1002ACJ	LT1007CDW
LP5907MFX- 2.85/NOPB	LPC662AMJ/883	LT1002ACN	LT1007CH
	LPC662IM	LT1002AMJ	LT1007CJ8
LP5907MFX- 3.2/NOPB	LPC662IN	LT1002CJ	LT1007CN8
LP5907SNX- 2.85/NOPB	LPV321M5	LT1002CN	LT1007CP
	LPV321M7	LT1002MJ	LT1007CS
LP5907SNX- 3.2/NOPB	LPV324M	LT1006ACH	LT1007MH
	LPV324MT	LT1006ACJ8	LT1007MJ8
LP5907SNX- 4.0/NOPB	LPV358MM	LT1006AMH	LT1007MJG
	LPV358MX	LT1006AMJ8	LT1007ML

Multisim 14.1 Education Components

LT1007MP	LT1013AIP	LT1014CJ	LT1022CN8
LT1008CH	LT1013AMFK	LT1014CN	LT1022MH
LT1008CN8	LT1013AMH	LT1014DN	LT1024ACN
LT1008MH	LT1013AMJ8	LT1014MJ	LT1024AMD
LT1008S8	LT1013AMP	LT1016CN8	LT1024CN
LT1010CDD	LT1013CH	LT1016CS8	LT1024MD
LT1010CH	LT1013CJ8	LT1016IN8	LT1028
LT1010CN8	LT1013CN8	LT1016IS8	LT1028ACH
LT1010CT	LT1013CP	LT1017CN8	LT1028ACJ8
LT1010MH	LT1013DD	LT1017CS8	LT1028ACN8
LT1011CN8	LT1013DID	LT1017CSW	LT1028AMH
LT1011CS8	LT1013DIP	LT1018CN8	LT1028AMJ8
LT1012	LT1013DMD	LT1018CS8	LT1028CH
LT1012ACH	LT1013DMJG	LT1018CSW	LT1028CJ8
LT1012ACN8	LT1013DMP	LT1021BCH-5	LT1028CN8
LT1012AMH	LT1013DN8	LT1021BCN8-10	LT1028CS
LT1012CH	LT1013DP	LT1021BCN8-5	LT1028MH
LT1012CN8	LT1013IP	LT1021BCN8-7	LT1028MJ8
LT1012DH	LT1013MFK	LT1021BMH-10	LT1037ACH
LT1012DN8	LT1013MH	LT1021DCS8-10	LT1037ACJ8
LT1012MH	LT1013MJ8	LT1021DCS8-5	LT1037ACN8
LT1012S8	LT1013MJG	LT1021DCS8-7	LT1037ACP
LT1013ACH	LT1013MP	LT1022ACH	LT1037AMH
LT1013ACJ8	LT1014ACJ	LT1022AMH	LT1037AMJ8
LT1013ACP	LT1014AMJ	LT1022CH	LT1037AMJG

Multisim 14.1 Education Components

LT1037AML	LT1057ACH	LT1077CJ8	LT1084CT
LT1037AMP	LT1057ACJ8	LT1077CN8	LT1085CM
LT1037CDW	LT1057ACN8	LT1077IN8	LT1085CT
LT1037CH	LT1057AMH	LT1077IS8	LT1097CN8
LT1037CJ8	LT1057AMJ8	LT1077MH	LT1097S8
LT1037CN8	LT1057CH	LT1077MJ8	LT1101ACH
LT1037CP	LT1057CJ8	LT1077S8	LT1101ACJ8
LT1037CS	LT1057CN8	LT1078ACH	LT1101ACN8
LT1037MH	LT1057IS	LT1078ACN8	LT1101AIN8
LT1037MJ8	LT1057MH	LT1078AMJ8	LT1101AMH
LT1037MJG	LT1057MJ8	LT1078CN8	LT1101AMJ8
LT1037ML	LT1057S	LT1078IN8	LT1101CH
LT1037MP	LT1058ACJ	LT1078IS8	LT1101CJ8
LT1055ACH	LT1058ACN	LT1078MH	LT1101CN8
LT1055AMH	LT1058AMJ	LT1078MJ8	LT1101IN8
LT1055CH	LT1058CJ	LT1078S8	LT1101MH
LT1055CN8	LT1058CMJ	LT1079ACN	LT1101MJ8
LT1055MH	LT1058CN	LT1079AM	LT1101S
LT1055S8	LT1077ACH	LT1079CN	LT1102ACN8
LT1056ACH	LT1077ACJ8	LT1079IN	LT1102CN8
LT1056AMH	LT1077ACN8	LT1079ISW	LT1102IN8
LT1056CH	LT1077AIN8	LT1079MJ	LT1112S8
LT1056CN8	LT1077AMH	LT1079SW	LT1113ACN8
LT1056MH	LT1077AMJ8	LT1083CP	LT1113CS8
LT1056S8	LT1077CH	LT1084CP	LT1114S

Multisim 14.1 Education Components

LT1115CN8	LT1126CS8	LT1178S	LT1191CN8
LT1115CS	LT1127CN	LT1179ACJ	LT1191CS8
LT1116CN8	LT1127CSW	LT1179ACN	LT1191MJ8
LT1116CS8	LT1128CN8	LT1179AMJ	LT1192CJ8
LT1121CN8	LT1128CS8	LT1179CJ	LT1192CN8
LT1121CS8	LT1129CQ	LT1179CN	LT1192CS8
LT1122ACJ8	LT1129CS8	LT1179IN	LT1192MJ8
LT1122ACN8	LT1129CT	LT1179MJ	LT1193CJ8
LT1122AMJ8	LT1167CN8	LT1179S	LT1193CN8
LT1122BCJ8	LT1167CS8	LT1179SW	LT1193CS8
LT1122BCN8	LT1168CN8	LT1187CJ8	LT1193MJ8
LT1122BMJ8	LT1168CS8	LT1187CN8	LT1194CJ8
LT1122CCJ8	LT1169CN8	LT1187CS8	LT1194CN8
LT1122CCN8	LT1169CS8	LT1187MJ8	LT1194CS8
LT1122CMJ8	LT1178ACH	LT1189CJ8	LT1194MJ8
LT1122CS8	LT1178ACJ8	LT1189CN8	LT1195CJ8
LT1122DCJ8	LT1178ACN8	LT1189CS8	LT1195CN8
LT1122DCN8	LT1178AMH	LT1189MJ8	LT1195CS8
LT1122DMJ8	LT1178AMJ8	LT118AH	LT1195MJ8
LT1122DS8	LT1178CH	LT118AJ8	LT1200
LT1124CN8	LT1178CJ8	LT1190CJ8	LT1201CN8
LT1124CS8	LT1178CN8	LT1190CN8	LT1201CS8
LT1125CN	LT1178IN8	LT1190CS8	LT1202CN
LT1125CSW	LT1178MH	LT1190MJ8	LT1202CS
LT1126CN8	LT1178MJ8	LT1191CJ8	LT1206CN8

Multisim 14.1 Education Components

LT1206CR	LT1215ACN8	LT1224CN8	LT1254CN
LT1206CS8	LT1215AMJ8	LT1224CS8	LT1254CS
LT1206CY	LT1215CN8	LT1225CN8	LT1256CN
LT1207CS	LT1215CS8	LT1225CS8	LT1256CS
LT1208CN8	LT1215MJ8	LT1226CN8	LT1259CN
LT1208CS8	LT1216CN	LT1226CS8	LT1259CS
LT1209CN	LT1216CS	LT1227CN8	LT1260CN
LT1209CS	LT1217CN8	LT1227CS8	LT1260CS
LT1210CR	LT1217CS8	LT1227MJ8	LT1328CMS8
LT1210CS	LT1218CN8	LT1228CN8	LT1328CS8
LT1210CT7	LT1218CS8	LT1228CS8	LT1351CMS8
LT1211ACN8	LT1219CN8	LT1229CJ8	LT1351CN8
LT1211AMJ8	LT1219CS8	LT1229CN8	LT1351CS8
LT1211CN8	LT1220CN8	LT1229CS8	LT1352CN8
LT1211CS8	LT1220CS8	LT1229MJ8	LT1352CS8
LT1211MJ8	LT1220MJ8	LT1230CJ	LT1353CS
LT1212CN	LT1221CN8	LT1230CN	LT1354CN8
LT1212CS	LT1221CS8	LT1230CS	LT1354CS8
LT1213ACN8	LT1221MJ8	LT1230MJ	LT1355CN8
LT1213AMJ8	LT1222CN8	LT1251CN	LT1355CS8
LT1213CN8	LT1222IS8	LT1251CS	LT1356CN
LT1213CS8	LT1223CJ8	LT1252CN8	LT1356CS
LT1213MJ8	LT1223CN8	LT1252CS8	LT1357CN8
LT1214CN	LT1223CS8	LT1253CN8	LT1357CS8
LT1214CS	LT1223MJ8	LT1253CS8	LT1358CN8

Multisim 14.1 Education Components

LT1358CS8	LT1395CS8	LT1464CN8	LT1494CS8
LT1359CN	LT1396CDD	LT1464CS8	LT1495CN8
LT1359CS	LT1396CMS8	LT1465CN	LT1495CS8
LT1359CS14	LT1396CS8	LT1465CS	LT1496CN
LT1360CN8	LT1397CGN	LT1466LCN8	LT1496CS
LT1360CS8	LT1397CS	LT1466LCS8	LT1497CS
LT1361CN8	LT1398CS	LT1467LCS	LT1497CS8
LT1361CS8	LT1399CGN	LT1468CDD	LT1498CN8
LT1362CN	LT1399CS	LT1468CN8	LT1498CS8
LT1362CS	LT1413ACN8	LT1468CS8	LT1499CS
LT1363CN8	LT1413CN8	LT1468IDD	LT1521CMS8
LT1363CS8	LT1413S8	LT1468IN8	LT1521CS8
LT1364CN8	LT1431CN8	LT1468IS8	LT1529CQ
LT1364CS8	LT1431CS8	LT1469CN8	LT1529CT
LT1365CN	LT1457CN8	LT1469CS8	LT1568CGN
LT1365CS	LT1457S8	LT1490CMS8	LT1568IGN
LT1366CN8	LT1461-25	LT1490CN8	LT1630CN8
LT1366CS8	LT1461-3	LT1490CS8	LT1630CS8
LT1367CS	LT1461-33	LT1491CN	LT1631CS
LT1368CN8	LT1461-4	LT1491CS	LT1632CN8
LT1368CS8	LT1461-5	LT1492CN8	LT1632CS8
LT1369CS	LT1462CN8	LT1492CS8	LT1633CS
LT1394CMS8	LT1462CS8	LT1493CS	LT1635CN8
LT1395CS5	LT1463CN	LT1494CMS8	LT1635CS8
LT1395CS6	LT1463CS	LT1494CN8	LT1636CDD

Multisim 14.1 Education Components

LT1636CMS8	LT1674CN	LT1722CS5	LT1763CDE-2.5
LT1636CN8	LT1674CS	LT1722CS8	LT1763CDE-3
LT1636CS8	LT1674IN	LT1723CMS8	LT1763CDE-3.3
LT1637CDD	LT1674IS	LT1723CS8	LT1763CDE-5
LT1637CMS8	LT1677CN8	LT1724CS	LT1763CS8
LT1637CN8	LT1677CS8	LT1739CFE	LT1763CS8-1.5
LT1637CS8	LT1678CS8	LT1739CUE	LT1763CS8-1.8
LT1638CDD	LT1679CS	LT1739IFE	LT1763CS8-2.5
LT1638CMS8	LT1711CMS8	LT1739IUE	LT1763CS8-3
LT1638CN8	LT1712CGN	LT1761ES5-1.8	LT1763CS8-3.3
LT1638CS8	LT1713CMS8	LT1761ES5-2	LT1763CS8-5
LT1639CN	LT1714CGN	LT1761ES5-2.5	LT1763IS8
LT1639CS	LT1715CMS	LT1761ES5-3	LT1763IS8-1.5
LT1671CMS8	LT1716CS5	LT1761ES5-3.3	LT1763IS8-1.8
LT1671CS8	LT1719CS8	LT1761ES5-5	LT1764EFE
LT1672CMS8	LT1719IS8	LT1761ES5-BYP	LT1764EFE-1.5
LT1672CN8	LT1720CDD	LT1761ES5-SD	LT1764EFE-1.8
LT1672CS8	LT1720CMS8	LT1762EMS8	LT1764EFE-2.5
LT1672IMS8	LT1720CS8	LT1762EMS8-2.5	LT1764EFE-3.3
LT1672IN8	LT1720IDD	LT1762EMS8-3	LT1764EQ
LT1672IS8	LT1720IMS8	LT1762EMS8-3.3	LT1764EQ-1.5
LT1673CN8	LT1720IS8	LT1762EMS8-5	LT1764EQ-1.8
LT1673CS8	LT1721CGN	LT1763CDE	LT1764EQ-2.5
LT1673IN8	LT1721CS	LT1763CDE-1.5	LT1764EQ-3.3
LT1673IS8	LT1721IGN	LT1763CDE-1.8	LT1782CS6

Multisim 14.1 Education Components

LT1783CS6	LT1801CMS8	LT1816ACMS	LT1884CS8
LT1784CS6	LT1801CS8	LT1816AIMS	LT1885CS
LT1784IS6	LT1802CS	LT1816CDD	LT1886CS8
LT1787CMS8	LT1806CS6	LT1816CMS8	LT1920CN8
LT1789CS8-1	LT1806CS8	LT1816CS8	LT1920CS8
LT1789CS8-10	LT1807CMS8	LT1816IDD	LT1962EMS8
LT1790ACS6-1.25	LT1807CS8	LT1816IMS8	LT1962EMS8-1.5
LT1790ACS6-2.048	LT1809CS6	LT1816IS8	LT1962EMS8-1.8
LT1790ACS6-2.5	LT1809CS8	LT1817CGN	LT1962EMS8-2.5
LT1790ACS6-3	LT1810CMS8	LT1817CS	LT1962EMS8-3
LT1790ACS6-3.3	LT1810CS8	LT1817IGN	LT1962EMS8-3.3
LT1790ACS6-4.096	LT1812CS5	LT1817IS	LT1962EMS8-5
LT1790ACS6-5	LT1812CS6	LT1818CS5	LT1963EFE
LT1792CN8	LT1812CS8	LT1818CS8	LT1963EFE-1.5
LT1792CS8	LT1813CDD	LT1818IS5	LT1963EFE-1.8
LT1793CN8	LT1813CS8	LT1818IS8	LT1963EFE-2.5
LT1793CS8	LT1813DMS8	LT1819CMS8	LT1963EFE-3.3
LT1794CFE	LT1814CGN	LT1819CS8	LT1970CFE
LT1794CSW	LT1814CS	LT1819IMS8	LT1990CS8
LT1795CFE	LT1815CS5	LT1819IS8	LT1991CDD
LT1795CSW	LT1815CS6	LT1880CS5	LT1991CMS
LT1797CS5	LT1815CS8	LT1881CN8	LT1993CUD-10
LT1800CS5	LT1815IS5	LT1881CS8	LT1993CUD-2
LT1800CS8	LT1815IS6	LT1882CS	LT1993CUD-4
LT1801CDD	LT1815IS8	LT1884CN8	LT1994CDD

Multisim 14.1 Education Components

LT1994CMS8	LT6002CDHC	LT6011CMS8	LT6220CS8
LT1995CDD	LT6002CGN	LT6011CS8	LT6221CDD
LT1995CMS	LT6002IDHC	LT6012CGN	LT6221CS8
LT1995IDD	LT6002IGN	LT6012CS	LT6222CGN
LT1995IMS	LT6003CDC	LT6100CDD	LT6230CS6
LT1996CDD	LT6003CS5	LT6100CMS8	LT6231CDD
LT1996CMS	LT6003HDC	LT6200CS6	LT6231CS8
LT2078ACS8	LT6003HS5	LT6200CS6-10	LT6232CGN
LT2078AIS8	LT6003IDC	LT6200CS6-5	LT6233CS6
LT2078CS8	LT6003IS5	LT6200CS8	LT6234CDD
LT2079ACS	LT6004CDD	LT6200CS8-10	LT6234CS8
LT2079CS	LT6004CMS8	LT6200CS8-5	LT6235CGN
LT2178ACS8	LT6004HDD	LT6201CDD	LT6235IGN
LT2178CS8	LT6004HMS8	LT6201CS8	LT6402CUD-12
LT2179ACS	LT6004IDD	LT6202CS5	LT6402CUD-20
LT2179CS	LT6004IMS8	LT6202CS8	LT6402CUD-6
LT318A	LT6005CDHC	LT6203CDD	LT6402IUD-12
LT318AJ8	LT6005CGN	LT6203CMS8	LT6402IUD-20
LT318AN8	LT6005HDHC	LT6203CS8	LT6402IUD-6
LT6000CDCB	LT6005HGN	LT6204CGN	LT6411CUD
LT6000IDCB	LT6005IDHC	LT6204CS	LT6411IUD
LT6001CDD	LT6005IGN	LT6205CS5	LT6552CDD
LT6001CMS8	LT6010CDD	LT6206CMS8	LT6552CS8
LT6001IDD	LT6010CS8	LT6207CGN	LT6552IDD
LT6001IMS8	LT6011CDD	LT6220CS5	LT6552IS8

Multisim 14.1 Education Components

LT6553CGN	LTC1047CS	LTC1052CP	LTC1442CN8
LT6553IGN	LTC1049CJ8	LTC1052CS	LTC1442CS8
LT6557CDHC	LTC1049CN8	LTC1052MD	LTC1443CDHD
LT6557CGN	LTC1049CS8	LTC1052MP	LTC1443CN
LT6557IDHC	LTC1050ACH	LTC1053CN	LTC1443CS
LT6557IGN	LTC1050ACJ8	LTC1053CS	LTC1444CDHD
LT6558CDHC	LTC1050ACN	LTC1053CSW	LTC1444CN
LT6558CGN	LTC1050ACN8	LTC1100CN8	LTC1444CS
LT6558IDHC	LTC1050AMH	LTC1100CSW	LTC1444IDHD
LT6558IGN	LTC1050AMJ8	LTC1150CJ8	LTC1444IN
LT6559CUD	LTC1050CH	LTC1150CN8	LTC1444IS
LT6600-10	LTC1050CJ8	LTC1150CS8	LTC1445CDHD
LT6600-2.5	LTC1050CN	LTC1150MJ8	LTC1445CN
LT6600-20	LTC1050CN8	LTC1151CN8	LTC1445CS
LT6600-5	LTC1050MH	LTC1151CSW	LTC152
LT6650CS5	LTC1050MJ8	LTC1152CN8	LTC1540CDD
LT6700CDCB-1	LTC1051ACJ8	LTC1152CS8	LTC1540CMS8
LT6700CDCB-2	LTC1051ACN8	LTC1250CN8	LTC1540CS8
LT6700CDCB-3	LTC1051ACS	LTC1250CS8	LTC1541CDD
LT6700CS6-1	LTC1051AMJ8	LTC1440CDD	LTC1541CMS8
LT6700CS6-2	LTC1051CJ8	LTC1440CMS8	LTC1541CS8
LT6700CS6-3	LTC1051CN8	LTC1440CN8	LTC1542CDD
LTC1043CN	LTC1051CS	LTC1440CS8	LTC1542CMS8
LTC1043CSW	LTC1051MJ8	LTC1441CN8	LTC1542CS8
LTC1047CN8	LTC1052CD	LTC1441CS8	LTC1563-2CGN

Multisim 14.1 Education Components

LTC1563-3CGN	LTC6078CDD	LTC6244IDD	MAC210-10
LTC1798CS8	LTC6078CMS8	LTC6244IMS8	MAC210-4
LTC1798CS8-2.5	LTC6079CDHC	LTC6800HDD	MAC210-6
LTC1798CS8-3	LTC6079CGN	LTC6800HMS8	MAC210-8
LTC1798CS8-4.1	LTC6101ACMS8	LTC6910-1CTS8	MAC210A-10
LTC1798CS8-5	LTC6101BCS5	LTC6910-2CTS8	MAC210A-4
LTC1841CS8	LTC6240CS5	LTC6910-3CTS8	MAC210A-6
LTC1842CS8	LTC6240CS8	LTC6911CMS-1	MAC210A-8
LTC1966CMS8	LTC6240HS5	LTC6911CMS-2	MAC212-10
LTC1967CMS8	LTC6240HS8	LTC7652CH	MAC212-4
LTC1968CMS8	LTC6240IS5	LTR-516AD	MAC212-6
LTC2050CS5	LTC6240IS8	LVL_BARGRAPH	MAC212-8
LTC2050CS6	LTC6241CDD	LVM_CURRENT	MAC212A-10
LTC2050CS8	LTC6241CS8	LVM_VOLTAGE	MAC212A-4
LTC2051CMS10	LTC6241HS8	M6060P-E3/45	MAC212A-6
LTC2052CGN	LTC6241IDD	MAC08MT1G	MAC212A-8
LTC2052CS	LTC6241IS8	MAC12HCDG	MAC223-10
LTC2053CDD	LTC6242CDHC	MAC15-10	MAC223-4
LTC2053CMS8	LTC6242CGN	MAC15-4	MAC223-6
LTC2053HDD	LTC6242HGN	MAC15-6	MAC223-8
LTC2053HMS8	LTC6242IDHC	MAC15-8	MAC223A-4
LTC2053IMS8-SYNC	LTC6242IGN	MAC15A-10	MAC223A-6
LTC2054CS5	LTC6244CDD	MAC15A-4	MAC223A-8
LTC2055CDD	LTC6244CMS8	MAC15A-6	MAC224-10
LTC2055CMS8	LTC6244HMS8	MAC15A-8	MAC224-4

Multisim 14.1 Education Components

MAC224-6	MAT03FH	MAX1446_FP32	MAX1666VEEP
MAC224-8	MAT04AY	MAX1449_FP32	MAX16814AGP/VY+
MAC224A-10	MAT04EY	MAX14802ECM+	MAX16814ATP+
MAC224A-4	MAT04FP	MAX14803AEWZ+	MAX16814AUP+
MAC224A-6	MAT04FS	MAX14803CCM+	MAX16820ATT+
MAC224A-8	MAT04FY	MAX15000AEUB+	MAX16823ATE+
MAC228-10	MAX1180_FP48	MAX15000BEUB+	MAX16823AUE+
MAC228-4	MAX1181_FP48	MAX15001AEUB+	MAX16826AGJ/VY+
MAC228-6	MAX1182_FP48	MAX15001BEUB+	MAX16826ATJ+
MAC228-8	MAX1183_FP48	MAX15004AAUE+	MAX16832AASA+
MAC228A-10	MAX1184_FP48	MAX15004BAUE+	MAX16832CASA+
MAC228A-4	MAX1185_FP48	MAX15005AAUE+	MAX16833AUE+
MAC228A-6	MAX1195_FP48	MAX15005BAUE+	MAX16834AGP/VY+
MAC228A-8	MAX1197_FP48	MAX15006AASA+	MAX16834ATP+
MAC23A-10	MAX1198_FP48	MAX15006AATT+	MAX16834AUP+
MAG_CMP4	MAX1284_SO8	MAX15007AASA+	MAX16838ATP+
MAG_OL	MAX1285_SO8	MAX15007AATT+	MAX16838AUP+
MAG_OL_RELAY	MAX1290_SO28	MAX15024AATB+	MAX16839ASA+
MAGNETIC_CORE_	MAX1291_SO28	MAX15024BATB+	MAX16839ATT+
VIRTUAL	MAX1292_SO24	MAX15024CATB+	MAX200CPP
MAGNETIC_FLUX	MAX1293_SO24	MAX15024DATB+T	MAX200ECWP
MAGNETIC_FLUX_G	MAX1420_FP48	MAX15025CATB+T	MAX200EEWP
ENERATOR	MAX1421_FP48	MAX16010TAA+	MAX200EPP
MAT02EH	MAX1422_FP48	MAX16010TAB+	MAX201CPD
MAT02FH	MAX1444_FP32	MAX16010TAC+	MAX201CWE
MAT03EH			

Multisim 14.1 Education Components

MAX201EPD	MAX205CPG	MAX209ENG	MAX221EEUE
MAX201EWE	MAX205E	MAX211	MAX232E
MAX202CPE	MAX205ECAG	MAX211CAI	MAX232ECPE
MAX202CSE	MAX205ECWG	MAX211E	MAX232EEPE
MAX202CWE	MAX205EEAG	MAX211EAI	MAX241E
MAX202ECPE	MAX205EEWG	MAX211ECAI	MAX241ECAI
MAX202ECUE	MAX206	MAX211ECWI	MAX241ECWI
MAX202EEPE	MAX206CAG	MAX211EEAI	MAX241EEAI
MAX202EEUE	MAX206E	MAX211EEWI	MAX241EEWI
MAX202ESE	MAX206EAG	MAX213	MAX253CPA+
MAX202EWE	MAX207	MAX213CAI	MAX253CSA+
MAX202SE	MAX207CAG	MAX213E	MAX253CUA+
MAX203CPP	MAX207E	MAX213EAI	MAX253EPA+
MAX203CWP	MAX207EAG	MAX213ECAI	MAX253ESA+
MAX203E	MAX207ECAG	MAX213ECWI	MAX253EUA+
MAX203ECPP	MAX207EEAG	MAX213EEAI	MAX253MJA
MAX203ECWP	MAX208	MAX213EEWI	MAX253MSA/PR
MAX203EPP	MAX208CAG	MAX218	MAX2740ECM
MAX203EERP	MAX208E	MAX218CAP	MAX274ACNG
MAX203EPP	MAX208EAG	MAX218CPP	MAX274ACWI
MAX203ERP	MAX208ECAG	MAX218EAP	MAX274BCNG
MAX204CPE	MAX208ECWG	MAX218EPP	MAX274BCWI
MAX204CWE	MAX208EEAG	MAX221ECAE	MAX317CJA
MAX204EPE	MAX208EEWG	MAX221ECUE	MAX317CPA+
MAX204EWE	MAX209	MAX221EEAE	MAX317CSA+

Multisim 14.1 Education Components

MAX317EJA	MAX3218EPP	MAX3243E	MAX4027EUD+
MAX317EPA+	MAX3221	MAX3243ECAI	MAX4028EUE+
MAX317ESA+	MAX3221CAE	MAX3243ECAP	MAX4028EWE+
MAX317MJA	MAX3221E	MAX3243ECPP	MAX4029EUP+
MAX318CJA	MAX3221EAE	MAX3243EEAI	MAX4029EWP+
MAX318CPA+	MAX3221ECAE	MAX3248E	MAX402CPA
MAX318CSA+	MAX3221EEAE	MAX3380E	MAX402CSA
MAX318EJA	MAX3222	MAX3381E	MAX402EPA
MAX318EPA	MAX3222E	MAX4004EUT+	MAX402ESA
MAX318ESA+	MAX3223	MAX4006EUT+	MAX4032EUT+
MAX318MJA	MAX3223E	MAX4007EUT+	MAX4032EXT+
MAX319CJA	MAX3223ECAP	MAX4008EUT+	MAX4036AAXK+
MAX319CPA+	MAX3223ECPP	MAX4012ESA+	MAX4036EXK+
MAX319CSA+	MAX3223ECUP	MAX4012EUK+	MAX4037EUT+
MAX319EJA	MAX3223EEAP	MAX4016ESA+	MAX4038AAUA+
MAX319EPA+	MAX3223EEPP	MAX4016EUA+	MAX4038EBL+T
MAX319ESA+	MAX3223EEUP	MAX4018EEE+	MAX4038ETA+
MAX319MJA	MAX3232	MAX4018ESD+	MAX4038EUA+
MAX3212	MAX3232E	MAX4020EEE+	MAX4039EBL+T
MAX3212CAI	MAX3237	MAX4020ESD+	MAX4039ETB+T
MAX3212EAI	MAX3237E	MAX4023EEE+	MAX4039EUB+
MAX3218	MAX3238E	MAX4023ESE+	MAX403CPA
MAX3218CAP	MAX3241	MAX4024ESD+	MAX403CSA
MAX3218CPP	MAX3241E	MAX4024EUD+	MAX403EPA
MAX3218EAP	MAX3243	MAX4027ESD+	MAX403ESA

Multisim 14.1 Education Components

MAX4069AUB+	MAX4080FAUA+	MAX409ACSA+	MAX410BCPA
MAX406ACPA+	MAX4080SASA+	MAX409AEPA	MAX410BCSA
MAX406ACSA+	MAX4080SAUA+	MAX409AESA+	MAX410BCSA+
MAX406AEPA+	MAX4080TASA+	MAX409AMJA	MAX410BEPA
MAX406AESA+	MAX4080TAUA+	MAX409BCPA+	MAX410BESA
MAX406AMJA	MAX4081FASA+	MAX409BCSA+	MAX410CPA
MAX406BCPA+	MAX4081FAUA+	MAX409BEPA+	MAX410CPA+
MAX406BCSA+	MAX4081SASA+	MAX409BESA+	MAX410CSA
MAX406BEPA+	MAX4081SAUA+	MAX4100ESA	MAX410CSA+
MAX406BESA+	MAX4081TASA+	MAX4100ESA+	MAX410EPA
MAX406BMJA	MAX4081TAUA+	MAX4100EUA+	MAX410EPA+
MAX4070ATA+	MAX4090AALT+T	MAX4101ESA	MAX410ESA+
MAX4070AUA+	MAX4090AAUT+	MAX4101ESA+	MAX410ETA-T
MAX4071ATA+	MAX4090AAXT+	MAX4104ESA	MAX4112ESA+
MAX4071AUA+	MAX4090ELT+T	MAX4104ESA+	MAX4112EUA
MAX4072ATA+	MAX4090EUT+	MAX4104EUK+	MAX4113ESA+
MAX4072AUA+	MAX4090EXT+	MAX4105ESA+	MAX4117ESA+
MAX4073TAUT+	MAX4091ASA+	MAX4105EUK+T	MAX4118ESA+
MAX4073TAXK+	MAX4091AUA+	MAX4106ESA	MAX4119EEE
MAX407CPA+	MAX4091AUK+	MAX4106ESA+	MAX4119ESD+
MAX407CSA+	MAX4092ASA+	MAX4107ESA	MAX4120ESD+
MAX407EPA+	MAX4092AUA+	MAX4107ESA+	MAX4122EUK+
MAX407ESA+	MAX4094ASD+	MAX4108ESA	MAX4124EUK+
MAX407MJA	MAX4094AUD+	MAX4108ESA+	MAX4126ESA+
MAX4080FASA+	MAX409ACPA+	MAX4109ESA+	MAX4126EUA+

Multisim 14.1 Education Components

MAX4128ESA+	MAX4132EUA+	MAX414MJD	MAX4178EUK+T
MAX4128EUA+	MAX4133ESD	MAX4162ESA+	MAX4178MJA
MAX4129ESD+	MAX4134ESD+	MAX4162EUK+	MAX417CPA+
MAX412BCPA	MAX4144EEE+	MAX4163EBL+	MAX417CSA+
MAX412BCPA+	MAX4144ESD+	MAX4163ESA+	MAX417EPA+
MAX412BCSA	MAX4145EEE+	MAX4163EUA+	MAX417ESA+
MAX412BCSA+	MAX4145ESD+	MAX4164ESD+	MAX417MJA
MAX412BEPA	MAX4146EEE+	MAX4165EUK+	MAX4180ESA+
MAX412BEPA+	MAX4146ESD+	MAX4166ELA+	MAX4180EUT+T
MAX412BESA	MAX4147ESD	MAX4166EPA+	MAX4181ESA+
MAX412BESA+	MAX4147ESD+	MAX4166ESA+	MAX4181EUT+T
MAX412CPA	MAX414BCPD	MAX4166EUA+	MAX4182ESA+
MAX412CPA+	MAX414BCSD	MAX4167EPA+	MAX4183ESD+
MAX412CSA	MAX414BCSD+	MAX4167ESA+	MAX4183EUB+
MAX412CSA+	MAX414BEPD	MAX4168EPD+	MAX4184ESA+
MAX412EPA	MAX414BESD	MAX4168ESD+	MAX4185ESD
MAX412EPA+	MAX414BESD+	MAX4168EUB+	MAX4185EUB+
MAX412ESA	MAX414CPD	MAX4169EPD	MAX4186ESD+
MAX412ESA+	MAX414CPD+	MAX4169ESD+	MAX4187EEE+
MAX412MJA	MAX414CSD	MAX4172EUA+	MAX4187ESD+
MAX4130EUK+	MAX414CSD+	MAX4173TESA+	MAX4188EEE+
MAX4131EBT+	MAX414EPD	MAX4173TEUT+	MAX4188ESD+
MAX4131ESA+	MAX414EPD+	MAX4178EPA+	MAX4189EEE+
MAX4131EUA+	MAX414ESD	MAX4178ESA+	MAX4189ESD+
MAX4132ESA+	MAX414ESD+	MAX4178EUA+	MAX418CPD+

Multisim 14.1 Education Components

MAX418CSD+	MAX4203ESA+	MAX4223ESA+	MAX4236BEUA+
MAX418EPD+	MAX4203EUA+	MAX4223EUT+	MAX4236EUT+
MAX418ESD+	MAX4204ESA+	MAX4224ESA+	MAX4237AESA+
MAX418MJD	MAX4204EUA+	MAX4224EUT+	MAX4237AEUA+
MAX4190ESA+	MAX4205ESA	MAX4225ESA+	MAX4237BESA+
MAX4190EUA	MAX4205EUA+	MAX4226ESD	MAX4237BEUA+
MAX4194ESA+	MAX4206ETE	MAX4226EUB+	MAX4237EUT+
MAX4195ESA+	MAX4212EUK+	MAX4227ESA+	MAX4238ASA+
MAX4196ESA+	MAX4213ESA+	MAX4228ESD+	MAX4238ATT+
MAX4197ESA+	MAX4213EUA+	MAX4228EUB+	MAX4238AUT+
MAX4198ESA+	MAX4214EUK+	MAX4230AUK+	MAX4239ASA+
MAX4198EUA+	MAX4215ESA+	MAX4230AXK+	MAX4239ATT+
MAX4199ESA+	MAX4215EUA+	MAX4231ART+T	MAX4239AUT+
MAX4199EUA+	MAX4216ESA+	MAX4231AUT+	MAX4240EUK+
MAX419CPD+	MAX4216EUA+	MAX4231AXT+	MAX4241ESA+
MAX419CSD+	MAX4217ESA+	MAX4231AYT+	MAX4241EUA+
MAX419EPD+	MAX4217EUA+	MAX4232AKA+	MAX4242ESA+
MAX419ESD+	MAX4218EEE+	MAX4232AUA+	MAX4242EUA+
MAX419MJD	MAX4218ESD+	MAX4233ABC+T	MAX4243ESD
MAX4200ESA+	MAX4219EEE+	MAX4233AUB+	MAX4243EUB+
MAX4200EUK+	MAX4219ESD+	MAX4234ASD+	MAX4244ESD+
MAX4201ESA+	MAX4220EEE+	MAX4234AUD+	MAX4245AUT+
MAX4201EUK+T	MAX4220ESD+	MAX4236AESA+	MAX4245AXT+
MAX4202ESA+	MAX4222EEE+	MAX4236AEUA	MAX4247AUB+
MAX4202EUK+T	MAX4222ESD+	MAX4236BESA+	MAX4249ESD+

Multisim 14.1 Education Components

MAX4249EUB+	MAX4269EEE	MAX4288EUB	MAX4333EUB+
MAX4250AAUK+	MAX4269ESD	MAX4289ESA+	MAX4334ESD+
MAX4250EUK+	MAX4270EEE	MAX4289EUT+	MAX4335EXT+
MAX4251ESA+	MAX4270ESD	MAX4291EUK+	MAX4336EUT-T
MAX4251EUA+	MAX4278EPA+	MAX4291EXK+	MAX4336EXT+
MAX4252EBL+	MAX4278ESA+	MAX4292EBL+	MAX4337EKA+
MAX4252ESA+	MAX4278EUA+	MAX4292ESA+	MAX4337EUA+
MAX4252EUA+	MAX4278EUK+	MAX4292EUA+	MAX4338EUB+
MAX4253EBC+	MAX4278MJA	MAX4294ESD+	MAX435CPD
MAX4253ESD+	MAX427CPA+	MAX4294EUD+	MAX435CSD
MAX4253EUB+	MAX427CSA+	MAX4304ESA+	MAX435CSD+
MAX4254ESD+	MAX427EPA+	MAX4304EUK+	MAX435EPD
MAX4255EUK+	MAX427ESA+	MAX4305ESA+	MAX435ESD
MAX4256ESA+	MAX427MJA	MAX4305EUK+	MAX435ESD+
MAX4256EUA+	MAX4281ESA+	MAX4323EBT+T	MAX435MJD
MAX4257ESA+	MAX4281EUK+	MAX4323ESA+	MAX4361ESA
MAX4257EUA+	MAX4282ESA+	MAX4323EUA	MAX4361EUA
MAX4265ESA+	MAX4282EUA+	MAX4323EUT+	MAX4362ESD+
MAX4265EUA+	MAX4284EEE	MAX4327ESD	MAX4362EUB+
MAX4266ESA+	MAX4284ESD	MAX4327EUB+	MAX4363EUP+
MAX4266EUA+	MAX4285ESA+	MAX4330EUK+	MAX436CPD
MAX4267ESA+	MAX4285EUT+	MAX4331ESA+	MAX436CSD
MAX4267EUA	MAX4286ESA+	MAX4331EUA+	MAX436CSD+
MAX4268EEE+	MAX4286EUT-T	MAX4332ESA+	MAX436EPD
MAX4268ESD+	MAX4288ESD	MAX4333ESD+	MAX436ESD

Multisim 14.1 Education Components

MAX436ESD+	MAX4375HESD+	MAX4384EUP+	MAX4403AUD+
MAX436MJD	MAX4375HEUB+	MAX4385EEUK+	MAX4412EUK+
MAX4372FEBT+T	MAX4375TESD+	MAX4386EESD+	MAX4412EXK+
MAX4372FESA+	MAX4375TEUB+	MAX4386EEUD+	MAX4413EKA+
MAX4372FEUK+	MAX4376FASA+T	MAX4388ESD+	MAX4414ESA+
MAX4372HEBT+T	MAX4376FAUK+T	MAX4388EUB	MAX4414EUA+
MAX4372HESA+	MAX4376HASA+T	MAX4389EUT+	MAX4415ESA+
MAX4372HEUK+	MAX4376HAUK+T	MAX4389EXT+	MAX4415EUA+
MAX4372TEBT+T	MAX4376TASA+T	MAX4390EUK+	MAX4416ESA+
MAX4372TESA+	MAX4376TAUK+T	MAX4390EXT+	MAX4416EUA+
MAX4372TEUK+	MAX437CPA	MAX4392ESA+	MAX4417ESA+
MAX4373FESA+	MAX437CSA+	MAX4392EUA+	MAX4417EUA+
MAX4373FEUA+	MAX437EPA	MAX4393EUB+	MAX4418EUD+
MAX4373HESA+	MAX437ESA+	MAX4394ESD+	MAX4419EUD+
MAX4373HEUA+	MAX437MJA	MAX4394EUD+	MAX44205ATC+
MAX4373TESA+	MAX4380EUT+	MAX4395ESD+	MAX44205AUB+
MAX4373TEUA+	MAX4380EXT+	MAX4395EUD+	MAX44206AUA+
MAX4374FESD+	MAX4381EUB+	MAX4396EUP+	MAX44211ETP+T
MAX4374FEUB+	MAX4382EEE+	MAX4400AUK+	MAX44241AUA+
MAX4374HESD+	MAX4382ESD+	MAX4400AXK+	MAX44241AUK+T
MAX4374HEUB+	MAX4382EUD+	MAX4401AXT+	MAX44242AKA+
MAX4374TESD+	MAX4383EEE+	MAX4402AKA+	MAX44242AUA+
MAX4374TEUB+	MAX4383ESD+	MAX4402ASA+	MAX44243ASD+
MAX4375FESD+	MAX4383ESE+	MAX4402AUA+	MAX44243AUD+
MAX4375FEUB+	MAX4383EUD+	MAX4403ASD+	MAX44244AUA+

Multisim 14.1 Education Components

MAX44244AUK+	MAX44284EAWT+	MAX4432EUA+	MAX4461HEUT+
MAX44245ASD+	MAX44284FAUT+	MAX4434ESA	MAX4461TESA+
MAX44245AUD+	MAX44284FAWT+	MAX4434EUK+	MAX4461TETT+
MAX44246ASA+	MAX44284HAUT+	MAX4435ESA	MAX4461TEUT
MAX44246AUA+	MAX44284HAWT+	MAX4435EUK	MAX4461UESA+
MAX44248ASA+	MAX44284WAUT+	MAX4436ESA	MAX4461UETT+T
MAX44248AUA+	MAX44284WAWT+	MAX4436EUA+	MAX4461UEUT-T
MAX44250AUA+	MAX44285FAUA+	MAX4437ESA	MAX4462HESA+
MAX44250AUK+	MAX44285FAWA+T	MAX4437EUA+	MAX4462HETT+
MAX44251AKA+	MAX44285HAUA+	MAX4444ESE+	MAX4462HEUT+
MAX44251AUA+	MAX44285HAWA+T	MAX4450EUK+	MAX4462TESA
MAX44252ASD+	MAX44285LAUA+	MAX4450EXK+	MAX4462TETT+T
MAX44260AXT+	MAX44285LAWA+T	MAX4451EKA+	MAX4462TEUT
MAX44260AYT+	MAX44285TAUA+	MAX4451ESA+	MAX4462UESA
MAX44263AXA+	MAX44285TAWA+T	MAX4452EUK+	MAX4462UETT+
MAX44264EWT+	MAX44286FAZS+T	MAX4452EXK+	MAX4464EUK+
MAX44265EWT+	MAX44286HAZS+T	MAX4453EKA+	MAX4464EXK+
MAX44267AUD+	MAX44286TAZS+T	MAX4453ESA+	MAX4473ESA
MAX44269EWL+	MAX44286WAZS+T	MAX4454ESD+	MAX4473EUA+
MAX44280AXT+	MAX44291AUA+	MAX4454EUD+	MAX4474EKA+
MAX44280AYT+	MAX44292ASA+T	MAX4460ESA+	MAX4474ESA+
MAX44281OANS+	MAX44294ASD+T	MAX4460ETT+	MAX4474EUA+
MAX44281UANS+	MAX4430ESA+	MAX4460EUT+T	MAX4475ASA+
MAX44281VANS+	MAX4430EUK+	MAX4461HESA+	MAX4475ATT+
MAX44284EAUT+	MAX4432ESA	MAX4461HETT+T	MAX4475AUA+

Multisim 14.1 Education Components

MAX4475AUT+	MAX4488AUA+	MAX4541EUA+	MAX4602EWE+
MAX4476ATT+T	MAX4488AUT+	MAX4542CSA+	MAX4603CAE+
MAX4476AUT+	MAX4489ASA+	MAX4542CUA	MAX4603CPE+
MAX4477ASA+	MAX4489AUA+	MAX4542EKA+	MAX4603CWE+
MAX4477AUA+	MAX4490AUK+T	MAX4542EPA	MAX4603EAE+
MAX4478ASD+	MAX4490AXK+	MAX4542ESA+	MAX4603EPE+
MAX4478AUD+	MAX4491AKA+	MAX4542EUA+	MAX4603EWE+
MAX4480AUK+	MAX4491AUA+	MAX4543CPA	MAX4659ESA+
MAX4480AXK+	MAX4492ASD+	MAX4543CSA	MAX4659EUA+
MAX4481AUT+	MAX4492AUD+	MAX4543CUA	MAX4660ESA+
MAX4481AXT+	MAX4493AUK	MAX4543EKA+	MAX4660EUA+
MAX4482AKA+	MAX4493AXK+	MAX4543EPA	MAX4667CPE
MAX4482ASA+	MAX4494AKA+	MAX4543ESA+	MAX4667CSE
MAX4482AUA+	MAX4494ASA+	MAX4543EUA+	MAX4667EPE
MAX4483ASD+	MAX4494AUA+	MAX4601CAE+	MAX4667ESE+
MAX4483AUD+	MAX4495ASD+	MAX4601CPE+	MAX4668CPE+
MAX4484AUK+	MAX4495AUD+	MAX4601CWE+	MAX4668CSE+
MAX4484AXK+	MAX4541CPA+	MAX4601EAE+	MAX4668EPE+
MAX4486AKA+	MAX4541CSA+	MAX4601EPE+	MAX4668ESE+
MAX4486ASA+	MAX4541CUA+	MAX4601EWE	MAX4669CPE
MAX4486AUA+	MAX4541EKA+	MAX4602CAE+	MAX4669CSE+
MAX4487ASD+	MAX4541EPA	MAX4602CPE+	MAX4669EPE
MAX4487AUD+	MAX4541ESA+	MAX4602CWE+	MAX4669ESE+
MAX4488ASA+	MAX4541ETA+T	MAX4602EAE+	MAX4670ETJ+
MAX4488ATT+	MAX4541EUA	MAX4602EPE	MAX4684EBC+

Multisim 14.1 Education Components

MAX4684ETB+	MAX474CSA	MAX478EPA+	MAX492CPA
MAX4684EUB+	MAX474CSA+	MAX478ESA+	MAX492CPA+
MAX4685EBC+T	MAX474CUA	MAX479ACPD	MAX492CSA
MAX4685ETB+T	MAX474CUA+	MAX479CPD+	MAX492CSA+
MAX4685EUB+	MAX474EPA+	MAX479CSD+	MAX492EPA+
MAX4714ELT+	MAX474ESA+	MAX479EPD+	MAX492ESA+
MAX4714EXT+	MAX474MJA	MAX479ESD+	MAX492MJA
MAX4717EBC+	MAX4754AEBE+T	MAX4800CCM+	MAX494CPD
MAX4717ETB+	MAX4754AETE+	MAX4800CQI+	MAX494CPD+
MAX4717EUB+	MAX4754EBE+T	MAX4800CTM+	MAX494CSD
MAX4718EBC-T	MAX4754ETE+	MAX4800CXZ+	MAX494CSD+
MAX4718EUB	MAX475CPD	MAX4801CQI+	MAX494EPD+
MAX4719EBC-T	MAX475CSD	MAX4818ETE+	MAX494ESD+
MAX4719EUB+	MAX475EPD	MAX4819ETE	MAX494MJD
MAX473CPA	MAX475ESD	MAX4885EETG+	MAX4951CTP+
MAX473CPA+	MAX475MJD	MAX4885ETJ+	MAX495CPA
MAX473CSA	MAX4766CETA+	MAX4887ETE+	MAX495CPA+
MAX473CSA+	MAX477EPA+	MAX4889AETO+	MAX495CSA
MAX473CUA	MAX477ESA+	MAX4890ETJ+	MAX495CSA+
MAX473CUA+	MAX477EUA+	MAX4891ETJ+	MAX495CUA
MAX473EPA+	MAX477EUK+T	MAX4892ETX+	MAX495CUA+
MAX473ESA+	MAX477MJA	MAX4906FELB+	MAX495EPA+
MAX473MJA	MAX478ACPA+	MAX4906FETB+T	MAX495ESA+
MAX474CPA	MAX478CPA+	MAX4907FELA+	MAX495MJA
MAX474CPA+	MAX478CSA+	MAX4907FETA+T	MAX496CPE+

Multisim 14.1 Education Components

MAX496CSE+	MAX5902ABETT+T	MAX5921AESA+	MAX6070BAUT12+ T
MAX497CPE+	MAX5902ABEUT+	MAX5941ACSE+	MAX6070BAUT18+ T
MAX497CSE+	MAX5902ABEUT-T	MAX5941AESE+	MAX6070BAUT21+ T
MAX5025EUT+	MAX5902ACETT+T	MAX5941BCSE+	MAX6070BAUT25+ T
MAX5027EUT+	MAX5902ACEUT+	MAX5941BESE+	MAX6070BAUT30+ T
MAX5035AASA+	MAX5902LAETT+	MAX5942ACSE+	MAX6070BAUT33+ T
MAX5035AUPA+	MAX5902LAEUT+	MAX5942AESE+	MAX6070BAUT41+ T
MAX5035AUSA+	MAX5902LBETT+T	MAX5942BCSE+	MAX6070BAUT50+ T
MAX5035BASA+	MAX5902LBEUT+T	MAX5942BESE+	MAX6126A21+T
MAX5035BUPA+	MAX5902LCETT+T	MAX5949AESA+	MAX6126A25+T
MAX5035BUS+T	MAX5902LCEUT+	MAX5953DUTM+	MAX6126A28+T
MAX5035CASA+	MAX5903AAETT+T	MAX6070AAUT12+ T	MAX6126A30+T
MAX5035CUPA+	MAX5903AAEUT+	MAX6070AAUT18+ T	MAX6126A41+T
MAX5035CUSA+	MAX5903ABETT+	MAX6070AAUT21+ T	MAX6126A50+T
MAX5048AATT+	MAX5903ABEUT+	MAX6070AAUT25+ T	MAX6324AUT23-T
MAX5048AAUT+T	MAX5903ACETT+	MAX6070AAUT30+ T	MAX6324AUT26-T
MAX5054AATA+	MAX5903ACEUT+	MAX6070AAUT33+ T	MAX6324AUT29+T
MAX5064AATC+	MAX5903LAETT+T	MAX6070AAUT41+ T	MAX6324AUT31+T
MAX5078AATT+	MAX5903LAEUT+	MAX6070AAUT50+ T	MAX6324AUT44-T
MAX5078BATT+	MAX5903LBETT+		MAX6324AUT46+T
MAX5631_QFN68	MAX5903LBEUT+		
MAX5632_QFN68	MAX5903LCETT+T		
MAX5633_QFN68	MAX5903LCEUT+		
MAX5902AAETT+	MAX5920AESA+		
MAX5902AAEUT+	MAX5920BESA+		

Multisim 14.1 Education Components

MAX6324BUT23+T	MAX6324FUT26+T	MAX6817EUT-TG1K	MAX809MEXR+
MAX6324BUT26-T	MAX6324FUT29-T	MAX706RCPA	MAX809REUR+
MAX6324BUT29+T	MAX6324FUT31-T	MAX706RCSA+	MAX809REXR+
MAX6324BUT31-T	MAX6324FUT44-T	MAX706RCUA+	MAX809SEUR+
MAX6324BUT44-T	MAX6324FUT46+T	MAX706REPA	MAX809SEXR+
MAX6324BUT46+T	MAX6324GUT23-T	MAX706RESA+	MAX809TEUR+
MAX6324CUT23+T	MAX6324GUT26+T	MAX706REUA+	MAX809TEXR+
MAX6324CUT26+T	MAX6324GUT29+T	MAX706RMJA	MAX809ZEXR+
MAX6324CUT29-T	MAX6324GUT31-T	MAX706TCPA+	MAX810LEUR+
MAX6324CUT31-T	MAX6324GUT44-T	MAX706TCSA+	MAX810LEXR+
MAX6324CUT44-T	MAX6324GUT46+T	MAX706TCUA+	MAX810MEUR+
MAX6324CUT46+T	MAX6324HUT23+T	MAX706TEPA	MAX810MEXR+
MAX6324DUT23+T	MAX6324HUT26-T	MAX706TESA+	MAX810REUR+
MAX6324DUT26+T	MAX6324HUT29+T	MAX706TEUA+	MAX810REXR+T
MAX6324DUT29-T	MAX6324HUT31+T	MAX706TMJA	MAX810SEUR+
MAX6324DUT31-T	MAX6324HUT44+T	MAX803LEXR+	MAX810SEXR+
MAX6324DUT44-T	MAX6324HUT46+T	MAX803MEXR+	MAX810TEUR+
MAX6324DUT46-T	MAX6460UT+	MAX803REXR+	MAX810TEXR+
MAX6324EUT23+T	MAX6495ATT+	MAX803SEXR+	MAX810ZEXR+T
MAX6324EUT26+T	MAX6780LTA+	MAX803TEXR+	MAX8815AETB+
MAX6324EUT29+	MAX6817EUT/GH9-T	MAX803ZEXR+	MAX9000ESA+
MAX6324EUT31-T	MAX6817EUT+	MAX809JEUR+	MAX9000EUA+
MAX6324EUT44-T	MAX6817EUT+T	MAX809LEUR+	MAX9002ESA+
MAX6324EUT46+T	MAX6817EUT-T	MAX809LEXR+	MAX9002EUA+
MAX6324FUT23+T		MAX809MEUR+	MAX9003ESA+

Multisim 14.1 Education Components

MAX9003EUA+	MAX903CSA+	MAX908EPD+	MAX912ESE+
MAX9005ESA+	MAX903EPA+	MAX908ESD	MAX912MJE
MAX9005EUA+	MAX903ESA+	MAX908ESD+	MAX913CPA
MAX9010EXT+	MAX9060EBS+G45	MAX908MJD	MAX913CPA+
MAX9011EUT+	MAX9060EUK+	MAX9092AKA+T	MAX913CSA
MAX9012ESA+	MAX9075EUK+	MAX9092AUA+	MAX913CSA+
MAX9012EUA+	MAX9075EXK+	MAX9094ASD+	MAX913EPA
MAX9013ESA+	MAX9077EKA+	MAX9094AUD+	MAX913EPA+
MAX9013EUA+	MAX9077ESA+	MAX909CPA	MAX913ESA
MAX9015AEKA+	MAX9077EUA+	MAX909CSA	MAX913ESA+
MAX9018AEKA+	MAX9077MSA/PR2	MAX909EPA	MAX913EUA+
MAX9025EBT+T	MAX907CPA	MAX909ESA	MAX913MJA
MAX9026EBT+	MAX907CPA+	MAX909MJA	MAX913MSA/PR
MAX9030AUT+	MAX907CSA	MAX9117ESA+	MAX9140AAUK+
MAX9030AXT+	MAX907CSA+	MAX9117EXK+	MAX9140AAXK+
MAX9031AUK+	MAX907EPA	MAX9119EXK+	MAX9140EUK+
MAX9031AXK+	MAX907EPA+	MAX9120ESA	MAX9140EXK+
MAX9032AKA+	MAX907ESA	MAX9120EXK+	MAX9141EKA+
MAX9032ASA+	MAX907ESA+	MAX912CPE	MAX9141ESA+
MAX9032AUA+	MAX907MJA	MAX912CPE+	MAX9142EKA+
MAX9034ASD+	MAX908CPD	MAX912CSE	MAX9142ESA+
MAX9034AUD+	MAX908CPD+	MAX912CSE+	MAX9144ESD+
MAX9038BABT+T	MAX908CSD	MAX912EPE	MAX9144EUD+
MAX9038BEBT+T	MAX908CSD+	MAX912EPE+	MAX9201ESE+
MAX903CPA+	MAX908EPD	MAX912ESE	MAX9201EUE+

Multisim 14.1 Education Components

MAX9202ESD+	MAX923CPA	MAX932CPA+	MAX941CPA
MAX9202EUD+	MAX923CPA+	MAX932CSA	MAX941CPA+
MAX9203EKA+	MAX923CSA	MAX932CSA+	MAX941CSA
MAX9203ESA+	MAX923CSA+	MAX932CUA+	MAX941CSA+
MAX921CPA	MAX923CUA	MAX932EPA	MAX941CUA
MAX921CPA+	MAX923CUA+	MAX932EPA+	MAX941EPA
MAX921CSA	MAX923EPA	MAX932ESA	MAX941EPA+
MAX921CSA+	MAX923EPA+	MAX932ESA+	MAX941ESA
MAX921CUA	MAX923ESA	MAX933CPA	MAX941ESA+
MAX921CUA+	MAX923ESA+	MAX933CPA+	MAX941EUA+
MAX921EPA	MAX923MJA	MAX933CSA	MAX941MJA
MAX921EPA+	MAX924CPE	MAX933CSA+	MAX942AUA+
MAX921ESA	MAX924CPE+	MAX933CUA+	MAX942CPA
MAX921ESA+	MAX924CSE	MAX933EPA	MAX942CPA+
MAX921MJA	MAX924CSE+	MAX933EPA+	MAX942CSA
MAX922CPA	MAX924EPE	MAX933ESA	MAX942CSA+
MAX922CPA+	MAX924EPE+	MAX933ESA+	MAX942CUA+
MAX922CSA	MAX924ESE	MAX934CPE	MAX942EPA
MAX922CSA+	MAX924ESE+	MAX934CPE+	MAX942EPA+
MAX922CUA+	MAX924MJE	MAX934CSE	MAX942ESA
MAX922EPA	MAX931CPA	MAX934CSE+	MAX942ESA+
MAX922EPA+	MAX931CSA	MAX934EPE	MAX942EUA+
MAX922ESA	MAX931EPA	MAX934EPE+	MAX942MJA
MAX922ESA+	MAX931ESA	MAX934ESE	MAX944CPD
MAX922MJA	MAX932CPA	MAX934ESE+	MAX944CPD+

Multisim 14.1 Education Components

MAX944CSD	MAX953EUA+	MAX9620AXK+	MAX9638AVB+
MAX944CSD+	MAX953MJA	MAX9621AUB/V+	MAX963ESA
MAX944EPD	MAX954CPA	MAX9621AUB/V+T	MAX963ESD+
MAX944EPD+	MAX954CSA	MAX9621AUB+	MAX9643TATA+T
MAX944ESD	MAX954EPA	MAX9621AUB+T	MAX9643UATA+T
MAX944ESD+	MAX954EPA+	MAX9622AXK+	MAX9644EBS+G45
MAX944MJD	MAX954ESA	MAX9626ATC+	MAX9644EUK+
MAX951EPA+	MAX954ESA+	MAX9627ATC+	MAX9645EUK+
MAX951ESA+	MAX954EUA+	MAX9628ATC+	MAX9647AUK+T
MAX951EUA+	MAX954MJA	MAX962ESA	MAX9647AXK+T
MAX951MJA	MAX9550EUA+	MAX9632ASA+	MAX9648AUK+
MAX952CPA	MAX9550EZK+	MAX9632ATA+	MAX9648AXK+
MAX952CSA	MAX9551EUA+	MAX9632AUA+	MAX964ESA
MAX952EPA	MAX9552EUD+	MAX9633ASA+	MAX9650ATA+
MAX952EPA+	MAX9600EUP+	MAX9633ATA+	MAX9650AUA+
MAX952ESA	MAX9601EUP+	MAX9634FERS+	MAX9650AZK+
MAX952ESA+	MAX9602EUG+	MAX9634FEUK+	MAX9651ATA+
MAX952EUA+	MAX9613AXT+	MAX9634HERS+	MAX9651AUA+
MAX952MJA	MAX9615AXA+	MAX9634HEUK+	MAX965ESA+
MAX953CPA	MAX9617AXT+	MAX9634TERS+	MAX965EUA+
MAX953CSA	MAX9618AXA+	MAX9634TEUK+	MAX9691EPA+
MAX953EPA	MAX9619AXT+	MAX9634WERS+	MAX9691ESA+
MAX953EPA+	MAX961ESA	MAX9634WEUK+	MAX9691EUA+
MAX953ESA	MAX961ESA+	MAX9636AXT+	MAX9692EPE+
MAX953ESA+	MAX961EUA+	MAX9637AXA+	MAX9692ESE+

Multisim 14.1 Education Components

MAX9692EUB+	MAX988EXK+	MAX9924UAUB+	MAX9938WEUK+
MAX9693EEE+	MAX989EKA+	MAX9924UAUB+T	MAX993ESD+
MAX9693EPE+	MAX989ESA+	MAX9926UAEE/V+	MAX993EUD+
MAX9693ESE+	MAX989EUA+	MAX9926UAEE/V+T	MAX9940AXK+
MAX975ESA+	MAX990EKA+	MAX9926UAEE+	MAX9943ATT+T
MAX975EUA+	MAX990ESA+	MAX9926UAEE+T	MAX9943AUA+
MAX976ESA+	MAX990EUA+	MAX9928FABT+	MAX9944ASA+
MAX976EUA+	MAX9910EXK+	MAX9928FAUA+	MAX9944ATA+T
MAX976MUA/PR2	MAX9911EWT+	MAX9929FABT+	MAX994ESD+
MAX977EEE+	MAX9911EXT+	MAX9929FAUA+	MAX994EUD+
MAX977ESD+	MAX9912EKA+	MAX992EKA+	MAX995ESD+
MAX978EEE+	MAX9913EUB+	MAX992ESA+	MAX995EUD+
MAX978ESE+	MAX9915EXT+	MAX992EUA+	MAX996ESD+
MAX985EBT+T	MAX9916EKA+	MAX9934FART+	MAX996EUD+
MAX985ESA+	MAX9917EUB+	MAX9934FAUA+	MAX997ESA+
MAX985EUK+	MAX9918ASA+	MAX9934TART+	MAX997EUA+
MAX985EXK+	MAX9919FASA+	MAX9934TAUA+	MAX998ESA+
MAX986ESA+	MAX9919NASA+	MAX9938FEBS+T	MAX998EUT+
MAX986EUK+	MAX991EKA+	MAX9938FELT+	MAX999AAUK+5
MAX986EXK+	MAX991ESA+	MAX9938FEUK+	MAX999EUK+
MAX987ESA+	MAX991EUA+	MAX9938HEBS+T	MAXIM-MAXQ-HDR
MAX987EUK+	MAX9920ASA+	MAX9938HEUK+	MB6S-E3/80
MAX987EXK+	MAX9924UAUB/V+	MAX9938TEBS+T	MBD1057-C18
MAX988ESA+	MAX9924UAUB/V+	MAX9938TEUK+	MBD2057-C18
MAX988EUK+	T	MAX9938WEBS+	MBD3057-C18

Multisim 14.1 Education Components

MBD4057-C18	MBR1045MFST3G	MBR130T3G	MBR20045CT
MBD5057-C18	MBR1060	MBR140ESFT1G	MBR20100
MBD770DWT1G	MBR1060G	MBR140ESFT3G	MBR20100CTG
MBR030	MBR1080G	MBR140SFT1G	MBR20100CTH
MBR040	MBR1090G	MBR140SFT3G	MBR20200CTG
MBR0520L	MBR10H100CTG	MBR150G	MBR2030CTLG
MBR0520LT1	MBR10H100CTHE3/ 45	MBR150RLG	MBR2035CT
MBR0520LT1G	MBR10H100-E3/45	MBR1520	MBR2045CT
MBR0520LT3G	MBR10L60CTG	MBR1530	MBR2045CTG
MBR0530	MBR1100G	MBR1535CT	MBR2045EMFST1G
MBR0530T1	MBR1100RLG	MBR1535CTG	MBR2045EMFST3G
MBR0530T1G	MBR12035CT	MBR1540	MBR2045MFST1G
MBR0530T3G	MBR12045CT	MBR1545CT	MBR2045MFST3G
MBR0540T1	MBR120ESFT1G	MBR1545CT-E3/45	MBR2060CTG
MBR0540T1G	MBR120ESFT3G	MBR1545CTG	MBR2080CTG
MBR0540T3G	MBR120LSFT1G	MBR160G	MBR2090CTG
MBR10100	MBR120LSFT3G	MBR160RLG	MBR20H100CT/45
MBR10100G	MBR120VLSFT1G	MBR16100CTG	MBR20H100CTG
MBR10100MFST1G	MBR120VLSFT3G	MBR1635	MBR20H150CTG
MBR10100MFST3G	MBR1240MFST1G	MBR1635G	MBR20H200CT- E3/45
MBR1035	MBR1240MFST3G	MBR1645	MBR20L45CTG
MBR1035G	MBR130LSFT1G	MBR1645G	MBR20L60CTG
MBR1045	MBR130T1	MBR16H45-E3/45	MBR230LSFT1G
MBR1045G	MBR130T1G	MBR1H100SFT3G	MBR2520
MBR1045MFST1G		MBR20035CT	

Multisim 14.1 Education Components

MBR2530	MBR30H60CTG	MBR40250G	MBR5831H
MBR2535CT	MBR30L45CTG	MBR40250TG	MBR5H100MFST1G
MBR2535CTG	MBR30L60CTG	MBR4030	MBR6035
MBR2535CTL	MBR3100G	MBR4040	MBR6035B
MBR2535CTLG	MBR3100RLG	MBR4045PT-E3/45	MBR6035PF
MBR2540	MBR320M	MBR4045PTG	MBR6045
MBR2545CT	MBR320P	MBR4045WTG	MBR6045B
MBR2545CTG	MBR330M	MBR4060PT-E3/45	MBR6045H
MBR2H100SFT3G	MBR330P	MBR40H100WTG	MBR6045PF
MBR30035CT	MBR340	MBR40L45CTG	MBR6045PTG
MBR30045CT	MBR340G	MBR40L60CTG	MBR6045WTG
MBR3020CT	MBR340M	MBR41H100CTG	MBR60H100CTG
MBR3035CT	MBR340P	MBR440MFST1G	MBR60L45CTG
MBR3035PT	MBR340RLG	MBR440MFST3G	MBR60L45WTG
MBR3045CT	MBR350RLG	MBR460MFST1G	MBR6535
MBR3045PT	MBR3520	MBR460MFST3G	MBR6545
MBR3045PTG	MBR3535	MBR5100MFST1G	MBR7030WTL
MBR3045STG	MBR3545	MBR5100MFST3G	MBR735
MBR3045WTG	MBR3545H	MBR540MFST1G	MBR735G
MBR30H100CTG	MBR360G	MBR540MFST3G	MBR745
MBR30H100MFST1 G	MBR360RLG	MBR560MFST1G	MBR745-E3/45
MBR30H100MFST3 G	MBR4015CTLG	MBR560MFST3G	MBR745G
MBR30H150CTG	MBR4015LWT	MBR5825	MBR7520
MBR30H30CTG	MBR4015LWTG	MBR5825H	MBR7530
	MBR4020	MBR5831	MBR7535

Multisim 14.1 Education Components

MBR7540	MBRAF440T3G	MBRB3030CTL	MBRD330RLG
MBR7545	MBRB1045G	MBRB3030CTLG	MBRD330T4G
MBR760-E3/45	MBRB1045T4G	MBRB3030CTT4G	MBRD340G
MBR7H45-E3/45	MBRB1545CTG	MBRB3045CT-1G	MBRD340RLG
MBR8035	MBRB1545CTT4	MBRB30H30CT-1G	MBRD340T4G
MBR8045	MBRB1545CTT4G	MBRB30H60CT-1G	MBRD350G
MBR8H100MFST1G	MBRB1645T4G	MBRB30H60CT-E3/81	MBRD350RLG
MBR8H100MFST3G	MBRB20100CTG	MBRB30H60CTT4G	MBRD350T4G
MBRA120ET3G	MBRB20100CTT4	MBRB4030	MBRD360G
MBRA130LT3	MBRB20100CTT4G	MBRB4030G	MBRD360RLG
MBRA130LT3G	MBRB20200CTG	MBRB4030T4G	MBRD360T4
MBRA140T3	MBRB20200CTT4	MBRB41H100CT-1G	MBRD360T4G
MBRA140T3G	MBRB20200CTT4G	MBRB41H100CTT4G	MBRD5H100T4G
MBRA160T3	MBRB2060CTG	G	MBRD620CTT4G
MBRA160T3G	MBRB2060CTT4G	MBRB60H100CTT4G	MBRD630CTT4G
MBRA1H100T3G	MBRB20H100CTT4G	G	MBRD640CTT4
MBRA210ET3G	MBRB2515LG	MBRB8H100T4G	MBRD640CTT4G
MBRA210LT3G	MBRB2515LT4G	MBRD1035CTL	MBRD650CTG
MBRA2H100T3G	MBRB2535CTLG	MBRD1035CTLG	MBRD650CTT4G
MBRA320T3G	MBRB2535CTLT4G	MBRD1035CTLT4G	MBRD660CTG
MBRA340T3G	MBRB2545CTG	MBRD1045T4G	MBRD660CTRLG
MBRAF1100T3G	MBRB2545CTT4G	MBRD320G	MBRD660CTT4G
MBRAF1540T3G	MBRB3030CT	MBRD320RLG	MBRD835L
MBRAF2H100T3G	MBRB3030CTG	MBRD320T4G	MBRD835LG
MBRAF3200T3G		MBRD330G	MBRD835LT4G

Multisim 14.1 Education Components

MBRF10H150CTG	MBRM120ET3G	MBRS190T3G	MBRS540T3G
MBRF10L60CTG	MBRM120LT1	MBRS2040LT3	MBT2222ADW1T1G
MBRF20100CTG	MBRM120LT1G	MBRS2040LT3G	MBT35200MT1
MBRF20200CTG	MBRM120LT3	MBRS230LT3G	MBT35200MT1G
MBRF2045CTG	MBRM120LT3G	MBRS240LT3	MBT3904DW1T1G
MBRF2060CTG	MBRM130LT1G	MBRS240LT3G	MBT3946DW1T1G
MBRF20H100CTG	MBRM130LT3	MBRS260T3G	MBT3946DW1T2G
MBRF20H150CTG	MBRM130LT3G	MBRS2H100T3G	MC1436CD
MBRF20L45CTG	MBRM140T1	MBRS3100T3G	MC1436CG
MBRF20L60CTG	MBRM140T1G	MBRS3200T3	MC1436CP1
MBRF20L80CTG	MBRM140T3	MBRS3200T3G	MC1436CU
MBRF2545CTG	MBRM140T3G	MBRS3201T3G	MC1436D
MBRF30H100CTG	MBRM1H100T3G	MBRS320T3	MC1436G
MBRF30H150CTG	MBRM2H100T3G	MBRS320T3G	MC1436P1
MBRF30H60CTG	MBRS1100T3	MBRS330T3G	MC1436U
MBRF30L45CTG	MBRS1100T3G	MBRS340T3	MC1437L
MBRF30L60CTG	MBRS120T3	MBRS340T3G	MC1437P
MBRF40250TG	MBRS120T3G	MBRS360BT3G	MC1439G
MBRL030	MBRS130LT3	MBRS360T3	MC1439P1
MBRL040	MBRS130LT3G	MBRS360T3G	MC1456CG
MBRM110ET1G	MBRS130T3G	MBRS410ET3G	MC1456CP1
MBRM110ET3G	MBRS140T3	MBRS410LT3	MC1456G
MBRM110LT1G	MBRS140T3G	MBRS410LT3G	MC1456P1
MBRM110LT3G	MBRS1540T3G	MBRS4201T3G	MC1458CD
MBRM120ET1G	MBRS190T3	MBRS540T3	MC1458CG

Multisim 14.1 Education Components

MC1458CP1	MC1709CG	MC1776CG	MC33072AP
MC1458CU	MC1709CP1	MC1776CP1	MC33072APG
MC1458D	MC1709CU	MC1776CU	MC33072D
MC1458G	MC1709G	MC1776G	MC33072DG
MC1458P	MC1741CD	MC1776U	MC33072DR2G
MC1458P1	MC1741CG	MC3301P	MC33072P
MC1458SD	MC1741CP1	MC3302DG	MC33072PG
MC1458SG	MC1741CU	MC3302DR2G	MC33072U
MC1458SP1	MC1741G	MC3302DTBR2G	MC33074ADG
MC1458SU	MC1741SCD	MC3302PG	MC33074ADR2G
MC1458U	MC1741SCG	MC3303D	MC33074ADTBG
MC1536G	MC1741SCP1	MC3303L	MC33074ADTBR2G
MC1536U	MC1741U	MC3303P	MC33074APG
MC1537L	MC1747CD	MC33071ADG	MC33074D
MC1539G	MC1747CG	MC33071ADR2G	MC33074DG
MC1556G	MC1747CL	MC33071AP	MC33074DR2G
MC1556U	MC1747CP2	MC33071APG	MC33074DTBG
MC1558FK	MC1747G	MC33071D	MC33074DTBR2G
MC1558G	MC1747L	MC33071DG	MC33074L
MC1558JG	MC1748CG	MC33071DR2G	MC33074P
MC1558SG	MC1748CP1	MC33071P	MC33074PG
MC1558SU	MC1748CU	MC33071PG	MC33077D
MC1558U	MC1748G	MC33071U	MC33077DG
MC1709AG	MC1748U	MC33072ADG	MC33077DR2G
MC1709AU	MC1776CD	MC33072ADR2G	MC33077P

Multisim 14.1 Education Components

MC33077PG	MC33178DG	MC33274P	MC34063ADG
MC33078D	MC33178DMR2G	MC33282D	MC34063ADR2G
MC33078DG	MC33178DR2G	MC33282P	MC34063AP1G
MC33078DR2G	MC33178P	MC33284D	MC34071D
MC33078P	MC33178PG	MC33284P	MC34071P
MC33078PG	MC33179D	MC33364D1G	MC34071U
MC33079D	MC33179DG	MC33364D1R2G	MC34080D
MC33079DG	MC33179DR2G	MC33364D2G	MC34080P
MC33079DR2G	MC33179DTBR2G	MC33364D2R2G	MC34084DW
MC33079P	MC33179P	MC3358P1	MC34084P
MC33079PG	MC33179PG	MC34001D	MC34161DG
MC33161DG	MC33181D	MC34001G	MC34161DMR2G
MC33161DMR2G	MC33181P	MC34001P	MC34161DR2G
MC33161DR2G	MC33182D	MC34001U	MC34161PG
MC33161PG	MC33182P	MC3401D	MC34181D
MC33171D	MC33184D	MC3401P	MC34181P
MC33171DG	MC33184P	MC3403D	MC3458D
MC33171DR2G	MC33272ADG	MC3403DG	MC3458G
MC33171P	MC33272APG	MC3403DR2G	MC3458P1
MC33171PG	MC33272D	MC3403L	MC3458U
MC33172D	MC33272P	MC3403N	MC3476G
MC33172P	MC33274ADG	MC3403P	MC3476P1
MC33174D	MC33274ADTBR2G	MC3403PG	MC3476U
MC33174P	MC33274APG	MC3405L	MC35001G
MC33178D	MC33274D	MC3405P	MC35001U

Multisim 14.1 Education Components

MC3503L	MCH3374-TL-W	MCH6613-TL-E	MCP6004T-E/ST
MC3505L	MCH3377-TL-E	MCH6661-TL-W	MCP601-I/P
MC35071AU	MCH3377-TL-H	MCH6663-TL-H	MCP601-I/SN
MC35071U	MCH3383-TL-H	MCH6663-TL-W	MCP601-I/ST
MC35080AU	MCH3474-TL-E	MCH6664-TL-W	MCP601T-I/OT
MC35080U	MCH3474-TL-H	MCP6001RT-E/OT	MCP6021-E/MS
MC35171U	MCH3479-TL-H	MCP6001RT-I/OT	MCP6021-I/P
MC35181U	MCH3479-TL-W	MCP6001T-E/LT	MCP6021-I/SN
MC3558G	MCH3484-TL-H	MCP6001T-E/OT	MCP6021-I/ST
MC3558U	MCH6203-TL-E	MCP6001T-I/LT	MCP6021T-E/OT
MC4558ACP1	MCH6320-TL-E	MCP6001T-I/OT	MCP6022-I/P
MC4558CD	MCH6321-TL-E	MCP6001UT-E/OT	MCP6022-I/SN
MC4558CG	MCH6336-TL-E	MCP6001UT-I/OT	MCP6022-I/ST
MC4558CP1	MCH6336-TL-H	MCP6002-E/MC	MCP6023-I/P
MC4558CU	MCH6337-TL-E	MCP6002-E/P	MCP6023-I/SN
MC4558G	MCH6337-TL-H	MCP6002-I/MS	MCP6023-I/ST
MC4558U	MCH6342-TL-H	MCP6002-I/P	MCP6024-I/P
MC4741CD	MCH6342-TL-W	MCP6002-I/SN	MCP6024-I/SL
MC4741CL	MCH6421-TL-E	MCP6002T-E/MS	MCP6024-I/ST
MC4741CP	MCH6436-TL-E	MCP6002T-E/SN	MCP602T-I/P
MC4741L	MCH6534-TL-E	MCP6004-E/P	MCP602T-I/SN
MCH3209-TL-E	MCH6541-TL-E	MCP6004-I/P	MCP602T-I/ST
MCH3333A-TL-H	MCH6601-TL-E	MCP6004-I/SL	MCP6031-E/MS
MCH3333A-TL-W	MCH6602-TL-E	MCP6004-I/ST	MCP6031-E/SN
MCH3374-TL-E	MCH6604-TL-E	MCP6004T-E/SL	MCP6031T-E/OT

Multisim 14.1 Education Components

MCP6032-E/MS	MCP604T-I/SL	MCP6074T-E/SL	MCP616-I/MS
MCP6032-E/SN	MCP604T-I/ST	MCP6074T-E/ST	MCP616-I/P
MCP6033-E/MS	MCP6051T-E/MNY	MCP607-I/P	MCP616-I/SN
MCP6033-E/SN	MCP6051T-E/OT	MCP607-I/SN	MCP617-I/MS
MCP6034-E/SL	MCP6051T-E/SN	MCP607-I/ST	MCP617-I/P
MCP6034-E/ST	MCP6052T-E/MNY	MCP608-I/P	MCP617-I/SN
MCP603T-I/CH	MCP6052T-E/SN	MCP608-I/SN	MCP618-I/MS
MCP603T-I/P	MCP6054T-E/SL	MCP608-I/ST	MCP618-I/P
MCP603T-I/SN	MCP6054T-E/ST	MCP609-I/P	MCP618-I/SN
MCP603T-I/ST	MCP6061T-E/MNY	MCP609-I/SL	MCP619-I/P
MCP6041-I/MS	MCP6061T-E/OT	MCP609-I/ST	MCP619-I/SL
MCP6041-I/P	MCP6061T-E/SN	MCP6141-I/MS	MCP619-I/ST
MCP6041-I/SN	MCP6062T-E/MNY	MCP6141-I/P	MCP621ST-E/OT
MCP6041T-I/OT	MCP6062T-E/SN	MCP6141-I/SN	MCP621T-E/MNY
MCP6042-I/MS	MCP6064T-E/SL	MCP6141T-E/OT	MCP621T-E/SN
MCP6042-I/P	MCP6064T-E/ST	MCP6142-I/MS	MCP622T-E/MF
MCP6042-I/SN	MCP606-I/P	MCP6142-I/P	MCP622T-E/SN
MCP6043-I/MS	MCP606-I/SN	MCP6142-I/SN	MCP6231-E/MC
MCP6043-I/P	MCP606-I/ST	MCP6143-I/MS	MCP6231-E/MS
MCP6043-I/SN	MCP606T-I/OT	MCP6143-I/P	MCP6231-E/P
MCP6043T-I/CH	MCP6071T-E/MNY	MCP6143-I/SN	MCP6231-E/SN
MCP6044-I/P	MCP6071T-E/OT	MCP6143T-E/CH	MCP6231RT-E/OT
MCP6044-I/SL	MCP6071T-E/SN	MCP6144-I/P	MCP6231T-E/OT
MCP6044-I/ST	MCP6072T-E/MNY	MCP6144-I/SL	MCP6231UT-E/LT
MCP604T-I/P	MCP6072T-E/SN	MCP6144-I/ST	MCP6231UT-E/OT

Multisim 14.1 Education Components

MCP6232-E/MS	MCP625T-E/UN	MCP6282-E/MS	MCP6293T-E/CH
MCP6232-E/P	MCP6271-E/MS	MCP6282-E/P	MCP6294-E/P
MCP6232-E/SN	MCP6271-E/P	MCP6282-E/SN	MCP6294-E/SL
MCP6232T-E/MNY	MCP6271-E/SN	MCP6283-E/MS	MCP6294-E/ST
MCP6234-E/P	MCP6271RT-E/OT	MCP6283-E/P	MCP6295-E/MS
MCP6234-E/SL	MCP6271T-E/OT	MCP6283-E/SN	MCP6295-E/P
MCP6234-E/ST	MCP6272-E/MS	MCP6283T-E/CH	MCP6295-E/SN
MCP623T-E/CHY	MCP6272-E/P	MCP6284-E/P	MCP629T-E/ML
MCP6241-E/MC	MCP6272-E/SN	MCP6284-E/SL	MCP631T-E/MNY
MCP6241-E/MS	MCP6273-E/MS	MCP6284-E/ST	MCP631T-E/OT
MCP6241-E/P	MCP6273-E/P	MCP6285-E/MS	MCP631T-E/SN
MCP6241-E/SN	MCP6273-E/SN	MCP6285-E/P	MCP632T-E/MF
MCP6241RT-E/OT	MCP6273T-E/CH	MCP6285-E/SN	MCP632T-E/SN
MCP6241T-E/OT	MCP6273T-E/SN	MCP6286T-E/OT	MCP633T-E/CHY
MCP6241UT-E/LT	MCP6274-E/P	MCP6291-E/MS	MCP633T-E/SN
MCP6241UT-E/OT	MCP6274-E/SL	MCP6291-E/P	MCP635T-E/MF
MCP6242-E/MS	MCP6274-E/ST	MCP6291-E/SN	MCP635T-E/UN
MCP6242-E/P	MCP6275-E/MS	MCP6291RT-E/OT	MCP6401RT-E/OT
MCP6242-E/SN	MCP6275-E/P	MCP6291T-E/OT	MCP6401T-E/LT
MCP6244-E/P	MCP6275-E/SN	MCP6292-E/MS	MCP6401T-E/OT
MCP6244-E/SL	MCP6281-E/MS	MCP6292-E/P	MCP6401T-H/OT
MCP6244-E/ST	MCP6281-E/P	MCP6292-E/SN	MCP6401UT-E/OT
MCP624T-E/SL	MCP6281-E/SN	MCP6293-E/MS	MCP6402T-E/MNY
MCP624T-E/ST	MCP6281RT-E/OT	MCP6293-E/P	MCP6402T-E/SN
MCP625T-E/MF	MCP6281T-E/OT	MCP6293-E/SN	MCP6402T-H/SN

Multisim 14.1 Education Components

MCP6404T-E/SL	MCP6474T-E/ST	MCP651T-E/SN	MCP6543T-E/MS
MCP6404T-E/ST	MCP6481T-E/LTY	MCP652T-E/MF	MCP6543T-E/SN
MCP6404T-H/SL	MCP6481T-E/OT	MCP652T-E/SN	MCP6543T-I/MS
MCP6406T-H/OT	MCP6482-E/MS	MCP653T-E/CHY	MCP6544-E/P
MCP6407T-H/SN	MCP6482-E/SN	MCP6541-E/P	MCP6544T-E/SL
MCP6409T-H/SL	MCP6482T-E/MNY	MCP6541-I/MS	MCP6544T-E/ST
MCP6421T-E/LTY	MCP6482T-E/MS	MCP6541-I/P	MCP6544T-I/P
MCP6421T-E/OT	MCP6482T-E/SN	MCP6541-I/SN	MCP6544T-I/SL
MCP6441T-E/LT	MCP6484-E/SL	MCP6541RT-E/OT	MCP6544T-I/ST
MCP6441T-E/OT	MCP6484-E/ST	MCP6541T-E/MS	MCP6546-E/P
MCP6442T-E/MNY	MCP6484T-E/SL	MCP6541T-E/OT	MCP6546-I/MS
MCP6442T-E/MS	MCP6484T-E/ST	MCP6541T-E/SN	MCP6546-I/P
MCP6442T-E/SN	MCP6491T-E/LTY	MCP6541T-I/LT	MCP6546-I/SN
MCP6444T-E/SL	MCP6491T-E/OT	MCP6541T-I/OT	MCP6546RT-E/OT
MCP6444T-E/ST	MCP6492-E/MS	MCP6541UT-E/OT	MCP6546RT-I/OT
MCP6471T-E/LTY	MCP6492-E/SN	MCP6541UT-I/LT	MCP6546T-E/MS
MCP6471T-E/OT	MCP6492T-E/MNY	MCP6542-E/P	MCP6546T-E/OT
MCP6472-E/MS	MCP6492T-E/MS	MCP6542-I/MS	MCP6546T-E/SN
MCP6472-E/SN	MCP6492T-E/SN	MCP6542-I/P	MCP6546T-I/LT
MCP6472T-E/MNY	MCP6494-E/SL	MCP6542-I/SN	MCP6546T-I/MS
MCP6472T-E/MS	MCP6494-E/ST	MCP6542T-E/MS	MCP6546T-I/OT
MCP6472T-E/SN	MCP6494T-E/SL	MCP6542T-E/SN	MCP6546T-I/SN
MCP6474-E/SL	MCP6494T-E/ST	MCP6543-E/P	MCP6546UT-E/OT
MCP6474-E/ST	MCP651ST-E/OT	MCP6543-I/P	MCP6546UT-I/LT
MCP6474T-E/SL	MCP651T-E/MNY	MCP6543-I/SN	MCP6547-E/P

Multisim 14.1 Education Components

MCP6547-I/MS	MCP655T-E/MF	MCP65R46T-2402E/CHY	MCP6H71T-E/SN
MCP6547-I/P	MCP655T-E/UN		MCP6H72-E/SN
MCP6547-I/SN	MCP6561RT-E/OT	MCP660T-E/ML	MCP6H72T-E/MNY
MCP6547T-E/MS	MCP6561T-E/LT	MCP660T-E/SL	MCP6H72T-E/SN
MCP6547T-E/SN	MCP6561T-E/OT	MCP660T-E/ST	MCP6H74-E/SL
MCP6547T-I/MS	MCP6561UT-E/OT	MCP661T-E/OT	MCP6H74-E/ST
MCP6547T-I/SN	MCP6562T-E/MS	MCP661T-E/SN	MCP6H74T-E/SL
MCP6548-E/P	MCP6562T-E/SN	MCP662T-E/MF	MCP6H74T-E/ST
MCP6548-I/MS	MCP6564T-E/SL	MCP662T-E/MS	MCP6H81-E/SN
MCP6548-I/P	MCP6564T-E/ST	MCP662T-E/SN	MCP6H81T-E/MNY
MCP6548-I/SN	MCP6566RT-E/OT	MCP663T-E/CHY	MCP6H81T-E/SN
MCP6548T-E/MS	MCP6566T-E/LT	MCP663T-E/SN	MCP6H82-E/SN
MCP6548T-E/SN	MCP6566T-E/OT	MCP664T-E/SL	MCP6H82T-E/MNY
MCP6548T-I/MS	MCP6566UT-E/OT	MCP664T-E/ST	MCP6H82T-E/SN
MCP6548T-I/SN	MCP6567T-E/MS	MCP665T-E/MF	MCP6H84-E/SL
MCP6549-E/P	MCP6567T-E/SN	MCP665T-E/UN	MCP6H84-E/ST
MCP6549-I/P	MCP6569T-E/SL	MCP669T-E/ML	MCP6H84T-E/SL
MCP6549-I/SL	MCP6569T-E/ST	MCP6H01T-E/MNY	MCP6H84T-E/ST
MCP6549-I/ST	MCP659T-E/ML	MCP6H01T-E/SN	MCP6H91T-E/MNY
MCP6549T-E/SL	MCP65R41T-1202E/CHY	MCP6H02T-E/MNY	MCP6H91T-E/SN
MCP6549T-E/ST		MCP6H02T-E/SN	MCP6H92T-E/MNY
MCP6549T-I/SL	MCP65R41T-2402E/CHY	MCP6H04T-E/SL	MCP6H92T-E/SN
MCP6549T-I/ST	MCP65R46T-1202E/CHY	MCP6H04T-E/ST	MCP6H94T-E/SL
MCP654T-E/SL		MCP6H71-E/SN	MCP6H94T-E/ST
MCP654T-E/ST		MCP6H71T-E/MNY	MCP6L01RT-E/OT

Multisim 14.1 Education Components

MCP6L01T-E/LT	MCP6L91T-E/OT	MCP6V01T-E/MNY	MCP6V27-E/SN
MCP6L01T-E/OT	MCP6L91T-E/SN	MCP6V01T-E/SN	MCP6V27T-E/MD
MCP6L01UT-E/OT	MCP6L92T-E/MS	MCP6V02-E/MD	MCP6V27T-E/MS
MCP6L02T-E/MS	MCP6L92T-E/SN	MCP6V02-E/SN	MCP6V27T-E/SN
MCP6L02T-E/SN	MCP6L94T-E/SL	MCP6V03-E/MNY	MCP6V28T-E/MNY
MCP6L04T-E/SL	MCP6L94T-E/ST	MCP6V03-E/SN	MCP6V28T-E/MS
MCP6L04T-E/ST	MCP6N11-001E/SN	MCP6V06-E/SN	MCP6V28T-E/SN
MCP6L1RT-E/OT	MCP6N11-002E/SN	MCP6V06T-E/MNY	MCP6V31T-E/OT
MCP6L1T-E/MS	MCP6N11-005E/SN	MCP6V07-E/MD	MCP6V31UT-E/LT
MCP6L1T-E/OT	MCP6N11-010E/SN	MCP6V07-E/SN	MCP6V31UT-E/OT
MCP6L1T-E/SN	MCP6N11-100E/SN	MCP6V08-E/SN	MCP6V32-E/MS
MCP6L2T-E/MS	MCP6N11T-001E/MNY	MCP6V08T-E/MNY	MCP6V32T-E/MNY
MCP6L2T-E/SN	MCP6N11T-002E/MNY	MCP6V11T-E/OT	MCP6V32T-E/MS
MCP6L4T-E/SL	MCP6N11T-005E/MNY	MCP6V11UT-E/LT	MCP6V34-E/ST
MCP6L4T-E/ST	MCP6N11T-010E/MNY	MCP6V11UT-E/OT	MCP6V34T-E/ST
MCP6L71RT-E/OT	MCP6N11T-100E/MNY	MCP6V12-E/MS	MCP6V61T-E/OT
MCP6L71T-E/MS	MCP6N16-001E/MF	MCP6V12T-E/MNY	MCP6V61UT-E/LTY
MCP6L71T-E/OT	MCP6N16-001E/MS	MCP6V12T-E/MS	MCP6V61UT-E/OT
MCP6L71T-E/SN	MCP6N16-010E/MF	MCP6V14-E/ST	MCP6V62-E/MS
MCP6L72T-E/MS	MCP6N16-010E/MS	MCP6V14T-E/ST	MCP6V62T-E/MNY
MCP6L72T-E/SN	MCP6N16-100E/MF	MCP6V26T-E/MNY	MCP6V62T-E/MS
MCP6L74T-E/SL	MCP6N16-100E/MS	MCP6V26T-E/MS	MCP6V64-E/ST
MCP6L74T-E/ST	MCP6N16-100E/MS	MCP6V26T-E/SN	MCP6V64T-E/ST
MCP6L91RT-E/OT	MCP6N16-100E/MS	MCP6V27-E/MD	MCP6V71T-E/OT
MCP6L91T-E/MS	MCP6N16-100E/MS	MCP6V27-E/MS	MCP6V71UT-E/LTY

Multisim 14.1 Education Components

MCP6V71UT-E/OT	MCR100-3RLG	MCR3835_2	MDA2502
MCP6V72-E/MS	MCR1906_2	MCR3835_3	MDA2504
MCP6V72T-E/MNY	MCR1906_3	MCR3835_4	MDA2506
MCP6V72T-E/MS	MCR1906_4	MCR3835_5	MDA3500
MCP6V74-E/ST	MCR1906_6	MCR3835_6	MDA3501
MCP6V74T-E/ST	MCR1906_8	MCR3835_7	MDA3502
MCP6V81T-E/OT	MCR22_2	MCR3835_8	MDA3504
MCP6V81UT-E/LTY	MCR22_3	MCR3835_9	MDA3506
MCP6V81UT-E/OT	MCR22_4	MCR3935_1	MDA3508
MCP6V82-E/MS	MCR22_6	MCR3935_10	MDA3510
MCP6V82T-E/MNY	MCR22_8	MCR3935_2	MDA3550
MCP6V82T-E/MS	MCR220_5	MCR3935_3	MDA3551
MCP6V84-E/ST	MCR220_7	MCR3935_4	MDA920A1
MCP6V84T-E/ST	MCR220_9	MCR3935_5	MDA920A2
MCP6V91T-E/OT	MCR221_5	MCR3935_6	MDA920A3
MCP6V91UT-E/LTY	MCR221_7	MCR3935_7	MDA920A4
MCP6V91UT-E/OT	MCR221_9	MCR3935_8	MDA920A5
MCP6V92-E/MS	MCR3818_10	MCR3935_9	MDA920A6
MCP6V92T-E/MNY	MCR3818_2	MCR703AT4G	MDA920A7
MCP6V92T-E/MS	MCR3818_3	MCR706AT4G	MDA920A8
MCP6V94-E/ST	MCR3818_4	MCR716T4G	MDA920A9
MCP6V94T-E/ST	MCR3818_6	MCR8SNG	MDA970A1
MCR08BT1G	MCR3818_8	MCT6	MDA970A2
MCR08MT1G	MCR3835_1	MDA2500	MDA970A3
MCR100-3G	MCR3835_10	MDA2501	MDA970A5

Multisim 14.1 Education Components

MDA970A6	MINI-DIN3S	MJ21194G	MJD127G
MDA980-1	MINI-DIN4	MJ21195G	MJD127T4
MDA980-2	MINI-DIN4S	MJ21196G	MJD127T4G
MDA980-3	MINI-DIN5	MJ2955G	MJD148T4
MDA980-4	MINI-DIN5S	MJ4502G	MJD148T4G
MDA980-5	MINI-DIN6	MJ802G	MJD200
MDA980-6	MINI-DIN6S	MJB41CG	MJD200G
MDA990-1	MIPS-EJTAG-HDR	MJB41CT4G	MJD200RLG
MDA990-2	MJ11012G	MJB42CT4G	MJD200T4G
MDA990-3	MJ11015G	MJB44H11G	MJD210G
MDA990-4	MJ11016G	MJB44H11T4	MJD210RLG
MDA990-5	MJ11028G	MJB44H11T4G	MJD210T4
MDA990-6	MJ11032G	MJB45H11G	MJD210T4G
MGP11N60ED	MJ11033G	MJB45H11T4	MJD243G
MGSF1N02LT1G	MJ14002G	MJB45H11T4G	MJD243T4G
MGSF1N03LT1G	MJ15001G	MJD112-1G	MJD253-1G
MGSF1P02LT1	MJ15003G	MJD112G	MJD253T4G
MGSF2N02ELT1G	MJ15004G	MJD112RLG	MJD2955-1G
MGSF3441VT1	MJ15015G	MJD112T4G	MJD2955G
MGW21N60ED	MJ15016G	MJD117-1G	MJD2955T4G
MHD20N06C	MJ15022G	MJD117G	MJD3055G
MHD20N06G	MJ15023G	MJD117RLG	MJD3055T4G
MHD20N06P	MJ15024G	MJD117T4G	MJD31C1G
MICRO_4BIT_ALU	MJ15025G	MJD122G	MJD31CG
MINI-DIN3	MJ21193G	MJD122T4G	MJD31CRLG

Multisim 14.1 Education Components

MJD31CT4G	MJD45H11-1G	MJE171G	MJE4353G
MJD31T4G	MJD45H11G	MJE172G	MJE5730G
MJD32CG	MJD45H11RLG	MJE18002G	MJE5731AG
MJD32CRLG	MJD45H11T4G	MJE18004G	MJE5731G
MJD32CT4	MJD47G	MJE18006G	MJE5742G
MJD32CT4G	MJD47T4G	MJE18008G	MJE5850G
MJD32RLG	MJD50G	MJE180G	MJE5851G
MJD32T4G	MJD50T4G	MJE181G	MJE5852G
MJD340G	MJD5731T4G	MJE182G	MJE700G
MJD340RLG	MJD6039T4G	MJE200G	MJE702G
MJD340T4G	MJE13003G	MJE210G	MJE703G
MJD350G	MJE13005G	MJE243G	MJE800G
MJD350T4G	MJE13007G	MJE253G	MJE802G
MJD41CRLG	MJE13009G	MJE270G	MJE803G
MJD41CT4G	MJE15028G	MJE271G	MJF122G
MJD42C1G	MJE15029G	MJE2955TG	MJF127G
MJD42CG	MJE15030G	MJE3055TG	MJF15030G
MJD42CRLG	MJE15031G	MJE340	MJF15031G
MJD42CT4G	MJE15032	MJE340G	MJF18004G
MJD44E3T4G	MJE15032G	MJE3439G	MJF18008G
MJD44H11-1G	MJE15033	MJE344G	MJF2955G
MJD44H11G	MJE15033G	MJE350	MJF3055G
MJD44H11RLG	MJE15034G	MJE350G	MJF31CG
MJD44H11T4G	MJE15035G	MJE371G	MJF32CG
MJD44H11T5G	MJE170G	MJE4343G	MJF44H11G

Multisim 14.1 Education Components

MJF45H11G	MM3Z15VT1G	MM5Z24VT1G	MM5Z8V2T1G
MJH11021G	MM3Z18VT1G	MM5Z27VT1G	MM5Z9V1ST1G
MJH11022G	MM3Z20VT1G	MM5Z2V4ST1G	MM5Z9V1T1G
MJH6284G	MM3Z2V4T1G	MM5Z2V4T1G	MMBD101LT1G
MJH6287G	MM3Z2V7T1G	MM5Z2V7T1G	MMBD1201
MJL1302A	MM3Z30VT1G	MM5Z33VT1G	MMBD1202
MJL1302AG	MM3Z36VT1G	MM5Z36VT1G	MMBD1203
MJL21193G	MM3Z39VT1G	MM5Z3V0T1G	MMBD1204
MJL21194G	MM3Z3V0T1G	MM5Z3V3T1G	MMBD1205
MJL21195G	MM3Z3V3ST1G	MM5Z3V6T1G	MMBD2835LT1G
MJL21196G	MM3Z3V6T1G	MM5Z47VT1G	MMBD2836LT1G
MJL3281AG	MM3Z3V9T1G	MM5Z4V3T1G	MMBD2837LT1G
MJL4281AG	MM3Z43VT1G	MM5Z4V7ST1G	MMBD2838LT1G
MJL4302AG	MM3Z4V3ST1G	MM5Z4V7ST5G	MMBD301LT1
MJW18020G	MM3Z4V7T1G	MM5Z4V7T1G	MMBD301LT1G
MJW21196G	MM3Z5V1T1G	MM5Z5V1ST1G	MMBD301LT3G
MJW3281AG	MM3Z5V6ST1G	MM5Z5V1T1G	MMBD301M3T5G
MKP3V120G	MM3Z6V8ST1G	MM5Z5V6ST1G	MMBD352LT1G
MKP3V120RLG	MM3Z8V2ST1G	MM5Z5V6T1G	MMBD353LT1G
MKP3V240G	MM5Z10VT1G	MM5Z6V2ST1G	MMBD4148
MKP3V240RLG	MM5Z12VT1G	MM5Z6V2T1G	MMBD7000LT1
MM3Z10VT1G	MM5Z15VT1G	MM5Z6V8ST1G	MMBD7000LT1G
MM3Z12VST1G	MM5Z16VT1G	MM5Z6V8T1G	MMBD7000LT3G
MM3Z12VT1G	MM5Z18VT1G	MM5Z7V5T1G	MMBD717LT1G
MM3Z15VST1G	MM5Z20VT1G	MM5Z8V2ST1G	MMBD770T1G

Multisim 14.1 Education Components

MMBD914	MMBR951AL	MMBT4401LT3G	MMBTA06LT3G
MMBD914LT1	MMBR951L	MMBT4401M3T5G	MMBTA06WT1G
MMBD914LT1G	MMBR951LT1	MMBT4403LT1	MMBTA14LT1G
MMBD914LT3G	MMBT2222A	MMBT4403LT1G	MMBTA42
MMBF0201NLT1	MMBT2222ALT1	MMBT4403LT3G	MMBTA42LT1
MMBF0201NLT1G	MMBT2222ALT1G	MMBT4403M3T5G	MMBTA42LT1G
MMBF170LT1G	MMBT2222ALT3G	MMBT489LT1G	MMBTA42LT3G
MMBF4393LT1G	MMBT2369ALT1G	MMBT5401LT1	MMBTA56LT1
MMBF4393LT3G	MMBT2484LT1G	MMBT5401LT1G	MMBTA56LT1G
MMBFJ175LT1G	MMBT2484LT3G	MMBT5401LT3G	MMBTA56LT3G
MMBFJ177LT1G	MMBT2907ALT1	MMBT5551LT1	MMBTA63LT1G
MMBFJ309LT1G	MMBT2907ALT1G	MMBT5551LT1G	MMBTA92
MMBR5031LT1	MMBT2907ALT3G	MMBT5551LT3G	MMBTA92LT1G
MMBR521LT1	MMBT2907AM3T5 G	MMBT5551M3T5G	MMBTA92LT3G
MMBR571L	MMBT2907AWT1G	MMBT589LT1	MMBTH10-4LT1G
MMBR571LT1	MMBT3904	MMBT589LT1G	MMBTH10LT1G
MMBR901_B	MMBT3904LT1	MMBT6428LT1G	MMBTH10LT3G
MMBR901L	MMBT3904LT1G	MMBT6429LT1G	MMBV105GLT1G
MMBR901LT1	MMBT3904LT3G	MMBT6517LT1	MMBV3401LT1G
MMBR911LT1	MMBT3904TT1G	MMBT6517LT1G	MMBV3401LT3
MMBR920LT1	MMBT3906	MMBT6517LT3G	MMBV3401LT3G
MMBR931L	MMBT3906TT1G	MMBT6520LT1	MMBZ10VAL
MMBR931LT1	MMBT4401LT1	MMBT6520LT1G	MMBZ12VAL
MMBR941	MMBT4401LT1G	MMBTA06LT1	MMBZ12VDL
MMBR941LT1		MMBTA06LT1G	MMBZ15VAL

Multisim 14.1 Education Components

MMBZ15VALT1	MMBZ5242BLT1G	MMQA20VT3G	MMSZ4692T1G
MMBZ15VALT1G	MMBZ5242BLT3G	MMQA5V6T1G	MMSZ4696T1G
MMBZ15VDL	MMBZ5248BLT1G	MMQA5V6T3G	MMSZ4699T1G
MMBZ15VDLT1G	MMBZ5248BLT3G	MMQA6V2T1G	MMSZ4705T1G
MMBZ15VDLT3G	MMBZ5254BLT1G	MMSD301T1	MMSZ4706T1G
MMBZ18VAL	MMBZ5256BLT1G	MMSD301T1G	MMSZ4707T1G
MMBZ18VCL	MMBZ5270BLT1G	MMSD4148T1	MMSZ4715T1G
MMBZ20VAL	MMBZ5V6AL	MMSD4148T1G	MMSZ5221BT1G
MMBZ20VALT1G	MMBZ5V6ALT1G	MMSD4148T3G	MMSZ5222BT1G
MMBZ20VCL	MMBZ5V6ALT3G	MMSF3P02HD	MMSZ5225BT1G
MMBZ27VAL	MMBZ6V2AL	MMSZ10T1G	MMSZ5226BT1G
MMBZ27VALT1G	MMBZ6V8AL	MMSZ12T1G	MMSZ5228BT1G
MMBZ27VALT3G	MMBZ9V1AL	MMSZ2V7T1G	MMSZ5231BT1G
MMBZ27VCL	MMDF3N04HD	MMSZ2V7T3G	MMSZ5231BT3G
MMBZ27VCLT1G	MMDF6N03HD	MMSZ3V3T1G	MMSZ5234BT1G
MMBZ33VAL	MMDL770T1G	MMSZ4678T1G	MMSZ5235BT1G
MMBZ33VALT1G	MMDL914T1	MMSZ4679T1G	MMSZ5235BT3G
MMBZ33VCL	MMDL914T1G	MMSZ4681T1G	MMSZ5236BT1G
MMBZ5221BLT1G	MMDL914T3G	MMSZ4683T1G	MMSZ5239BT1G
MMBZ5222BLT1G	MMFT5P03HD	MMSZ4688T1G	MMSZ5240BT1G
MMBZ5226BLT1G	MMFT960T1G	MMSZ4689T1G	MMSZ5242BT1G
MMBZ5231BLT1G	MMG05N60D	MMSZ4689T3G	MMSZ5242BT3G
MMBZ5231BLT3G	MMJT350T1G	MMSZ4690T1G	MMSZ5243BT1G
MMBZ5232BLT1G	MMQA15VT1G	MMSZ4690T3G	MMSZ5245BT1G
MMBZ5240BLT1G	MMQA20VT1G	MMSZ4691T1G	MMSZ5246BT1G

Multisim 14.1 Education Components

MMSZ5254BT1G	MMUN2114LT3G	MOS_N_4T_DEP	MPC506AP
MMSZ5258BT1G	MMUN2115LT1G	MOS_N_DEP	MPC506AU
MMSZ5258BT3G	MMUN2116LT1G	MOS_P	MPC507AP
MMSZ5259BT1G	MMUN2130LT1G	MOS_P_4T	MPC507AU
MMSZ5260BT1G	MMUN2131LT1G	MOS_P_4T_DEP	MPC508AP
MMSZ5262BT1G	MMUN2132LT1G	MOS_P_DEP	MPC508AU
MMSZ5263BT1G	MMUN2134LT1G	MOSFET_DIODE_THERMAL	MPC509AP
MMT05B230T3G	MMUN2211LT1G	Mosfet1_3TEN	MPC509AU
MMT05B260T3G	MMUN2211LT3G	MOTOR_1A	MPC-BDM-HDR
MMT05B310T3G	MMUN2212LT1G	MOTOR_1C	MPS2907AG
MMT05B350T3G	MMUN2213LT1G	MOTOR_2A	MPS2907ARLG
MMT08B064T3G	MMUN2214LT1G	MOTOR_2C	MPS2907ARLRAG
MMT08B260T3G	MMUN2215LT1G	MOTOR_3A	MPS2924
MMT08B310T3G	MMUN2216LT1G	MOTOR_3C	MPS2925
MMT08B350T3G	MMUN2231LT1G	MOTOR_4A	MPS2926
MMT10B230T3G	MMUN2232LT1G	MOTOR_4C	MPS3392
MMT10B260T3G	MMUN2233LT1G	Motor_dc1	MPS3393
MMT10B310T3G	MMUN2234LT1G	MOTOR_RATED	MPS3395
MMT10B350T3G	MMUN2238LT1G	MOTOR_VIRTUAL	MPS3638A
MMUN2111LT1G	MMVL3401T1G	MPC100AP	MPS3644
MMUN2111LT3G	MOC8101_BASSO	MPC100AU	MPS3646
MMUN2112LT1G	MONOSTABLE_VIRTUAL	MPC102AP	MPS3702
MMUN2113LT1G	MOS_N	MPC102AU	MPS3703
MMUN2113LT3G	MOS_N_4T	MPC104AP	MPS3704
MMUN2114LT1G			MPS3707

Multisim 14.1 Education Components

MPS3711	MPS8099	MPSA92	MPZ2012S221A
MPS3826	MPS8598	MPSA93	MPZ2012S300A
MPS3827	MPSA05	MPSH10	MPZ2012S331A
MPS3904	MPSA06	MPSL01	MPZ3216S500A
MPS5172	MPSA06G	MPSL51	MR1120
MPS5179	MPSA06RL1G	MPSW01	MR1366
MPS6512	MPSA06RLG	MPSW01A	MR1376
MPS6513	MPSA06RLRAG	MPSW06G	MR1386
MPS6514	MPSA06RLRMG	MPSW06RLRAG	MR1396
MPS6515	MPSA06RLRPG	MPSW10	MR2400
MPS6516	MPSA10	MPSW42	MR2400F
MPS6517	MPSA18	MPSW45G	MR2401
MPS6518	MPSA20	MPSW51	MR2401F
MPS6520	MPSA42	MPSW51A	MR2402
MPS6521	MPSA42G	MPSW51AG	MR2402F
MPS6522	MPSA43	MPSW51ARLRAG	MR2404
MPS6523	MPSA43G	MPSW51ARLRPG	MR2404F
MPS6531	MPSA55	MPSW51G	MR2406
MPS6533	MPSA56	MPSW55	MR2406F
MPS6534	MPSA56G	MPSW56	MR2500
MPS6562	MPSA56RLRAG	MPX2010DP	MR2501
MPS6565	MPSA56RLRMG	MPX2050DP	MR2502
MPS6566	MPSA56RLRPG	MPX2100DP	MR2504
MPS6571	MPSA56ZL1G	MPX2200DP	MR2506
MPS8098	MPSA70	MPZ2012S101A	MR2508

Multisim 14.1 Education Components

MR2510	MR810	MR862	MRF9331LT1
MR327	MR811	MR864	MRF9411BL
MR328	MR812	MR866	MRF9411L
MR330	MR813	MR870	MRF9411LT1
MR331	MR814	MR871	MRF947
MR500	MR816	MR872	MRF947T1
MR5005	MR817	MR874	MRF949T1
MR501	MR818	MR876	MRF9511AL
MR5010	MR820	MRA4003T3G	MRF9511L
MR502	MR821	MRA4004T3G	MRF9511LT1
MR5020	MR822	MRA4005T1G	MRS1504T3G
MR5030	MR824	MRA4005T3G	MSB92T1G
MR504	MR826	MRA4006T3G	MSD1328-RT1G
MR5040	MR830	MRA4007T3G	MSD602-RT1G
MR5059	MR831	MRF5211LT1	MSE1PJHM3/89A
MR506	MR832	MRF5711L	MSP3V3HM3/89A
MR5060	MR834	MRF5711LT1	MSQA6V1W5T2G
MR5061	MR836	MRF5812	MSR1560G
MR508	MR850	MRF8372	MSR860G
MR510	MR851	MRF9011L	MSRD620CTG
MR750	MR852	MRF9011LT1	MSRD620CTRG
MR751	MR854	MRF9011LT1_A	MSRD620CTT4
MR752	MR856	MRF9011LT1_B	MSRD620CTT4G
MR754	MR860	MRF917T1	MSRD620CTT4RG
MR756	MR861	MRF927T1	MSRF1560G

Multisim 14.1 Education Components

MSRF860G	MTD5P06V	MTP2P50EG	MUN2135T1G
MSS1P3LHM3/89A	MTD6N15T4G	MTP3055E/MC	MUN2138T1G
MSS1P4HM3/89A	MTD6N20E	MTP3055V	MUN2141T1G
MSS1P6HM3/89A	MTD6N20ET4G	MTP3055VL	MUN2211T1
MSS2P3HM3/89A	MTD6P10E	MTP30N08M	MUN2211T1G
MT4C4ME8DJ-5	MTDF1N03HD	MTP35N06E	MUN2211T3G
MTB20N20E	MTH13N50	MTP3N100	MUN2212T1G
MTB23P06V	MTH30N20	MTP40N06M	MUN2213T1
MTB2P50E	MTH5N100	MTP4N50	MUN2213T1G
MTB50P03HDL	MTH8N60	MTP4N85	MUN2214T1G
MTB50P03HDLT4G	MTM10N100E	MTP50N05EL	MUN2214T3G
MTD10P06HDL	MTM15N40	MTP50N06E	MUN2215T1G
MTD15N06V	MTM24N50E	MTP6N60	MUN2216T1G
MTD1N60E	MTM26N40E	MTP6N60/MC	MUN2230T1G
MTD1N80E	MTM8N60	MTP75N05C	MUN2232T1G
MTD20N06HD	MTP10N05E/MC	MTP7N20	MUN2233T1G
MTD20P03HDL	MTP12P10	MTP8N50E	MUN2234T1G
MTD2955E	MTP15N05E	MTP8P10	MUN2236T1G
MTD2N50E	MTP15N06E	MTSF3N02HD	MUN2237T1G
MTD3055V	MTP20P06	MULTIPLIER	MUN2238T1G
MTD3055VL	MTP25N06	MUN2111T1G	MUN2240T1G
MTD3N25E	MTP25N06L	MUN2112T1G	MUN5111DW1T1G
MTD4N20E	MTP25N10E	MUN2113T1G	MUN5111T1G
MTD4P06	MTP2N50	MUN2114T1G	MUN5112DW1T1G
MTD5N06	MTP2P50	MUN2115T1G	MUN5112T1G

Multisim 14.1 Education Components

MUN5113DW1T1G	MUN5215DW1T1G	MUN5335DW1T2G	MUR1510
MUN5113T1G	MUN5215T1G	MUN5336DW1T1G	MUR1510G
MUN5113T3G	MUN5216DW1T1G	MUR10005CT	MUR1515
MUN5114DW1T1G	MUN5230DW1T1G	MUR10010CT	MUR1515G
MUN5114T1G	MUN5230T1G	MUR10015CT	MUR1520
MUN5115DW1T1G	MUN5232DW1T1G	MUR10020CT	MUR1520G
MUN5115T1G	MUN5232T1G	MUR10150E	MUR1530
MUN5116DW1T1G	MUN5233DW1T1G	MUR105	MUR1540
MUN5131T1G	MUN5233T1G	MUR105G	MUR1540G
MUN5132T1G	MUN5235DW1T1G	MUR105RLG	MUR1550
MUN5133DW1T1G	MUN5237DW1T1G	MUR110	MUR1560
MUN5133T1G	MUN5238T1G	MUR1100EG	MUR1560G
MUN5135DW1T1G	MUN5240T1G	MUR1100ERLG	MUR160
MUN5135T1G	MUN5241T1G	MUR110G	MUR1605CT
MUN5140T1G	MUN5311DW1T1G	MUR110RLG	MUR160G
MUN5211DW1T1G	MUN5312DW1T1G	MUR115	MUR160RLG
MUN5211T1	MUN5312DW1T2G	MUR115G	MUR1610CT
MUN5211T1G	MUN5313DW1T1G	MUR115RLG	MUR1610CTG
MUN5212DW1T1G	MUN5314DW1T1G	MUR120G	MUR1615CT
MUN5212T1G	MUN5315DW1T1G	MUR120RLG	MUR1615CTG
MUN5213DW1T1G	MUN5316DW1T1G	MUR130G	MUR1620CT
MUN5213DW1T3G	MUN5330DW1T1G	MUR130RLG	MUR1620CTG
MUN5213T1G	MUN5333DW1T1G	MUR140G	MUR1620CTRG
MUN5214DW1T1G	MUN5334DW1T1G	MUR140RLG	MUR1640CTG
MUN5214T1G	MUN5335DW1T1G	MUR1505	MUR1660CTG

Multisim 14.1 Education Components

MUR180EG	MUR3060WTG	MUR550PFG	MURA115T3G
MUR180ERLG	MUR405	MUR605CT	MURA120T3
MUR2020RG	MUR405G	MUR610CT	MURA120T3G
MUR2100EG	MUR410	MUR615CT	MURA130T3G
MUR2100ERLG	MUR4100EG	MUR620CT	MURA140T3
MUR210G	MUR4100ERLG	MUR620CTG	MURA140T3G
MUR210RLG	MUR410G	MUR805	MURA160T3
MUR220G	MUR410RLG	MUR805G	MURA160T3G
MUR220RLG	MUR415	MUR810	MURA205T3G
MUR240G	MUR415G	MUR8100EG	MURA210T3G
MUR240RLG	MUR415RLG	MUR810G	MURA215T3
MUR2505	MUR420	MUR815	MURA215T3G
MUR2510	MUR420G	MUR815G	MURA220T3
MUR2515	MUR420RLG	MUR820	MURA220T3G
MUR2520	MUR440G	MUR820G	MURA230T3G
MUR260G	MUR440RLG	MUR830	MURA240T3G
MUR260RLG	MUR460G	MUR840	MURB1620CTG
MUR3005PT	MUR460RLG	MUR840G	MURB1620CTRG
MUR3010PT	MUR480EG	MUR850	MURB1620CTRT4G
MUR3015PT	MUR480ERLG	MUR860	MURB1620CTT4
MUR3020PT	MUR5005	MUR860G	MURB1620CTT4G
MUR3020PTG	MUR5010	MUR880EG	MURB1660CTG
MUR3020WTG	MUR5015	MURA105T3G	MURB1660CTT4G
MUR3040PTG	MUR5020	MURA110T3	MURD320T4
MUR3060PTG	MUR550APFRLG	MURA110T3G	MURD320T4G

Multisim 14.1 Education Components

MURD330T4G	MURS110T3G	MURS360T3G	MZ4616
MURD340T4G	MURS115T3	MURS480ET3G	MZ4617
MURD530T4G	MURS115T3G	MUSHROOM_HEAD	MZ4618
MURD550PFT4G	MURS120T3	MUX_16TO1	MZ4619
MURD620CT	MURS120T3G	MUX_2TO1	MZ4620
MURD620CTG	MURS140T3	MUX_4TO1	MZ4621
MURD620CTT4	MURS140T3G	MUX_8TO1	MZ4622
MURD620CTT4G	MURS160-E3/52T	MUX_LATCH	MZ4623
MURF1560G	MURS160T3	MUX2_1	MZ4624
MURF1620CTG	MURS160T3G	MUX2_1_INV	MZ4625
MURF1660CTG	MURS205T3G	MUX2_1INV_3S	MZ4626
MURF550PFG	MURS210T3G	MUX4_1	MZ4627
MURF860G	MURS220T3	MUX4_1_INVO	MZ5520B
MURH840CTG	MURS220T3G	MUX8_1	MZ5521B
MURH860CTG	MURS230T3	MVGSF1N03LT1G	MZ5522B
MURHB840CTG	MURS230T3G	MVMBF0201NLT1G	MZ5523B
MURHB840CTT4	MURS240T3G	myRIO_MXP	MZ5524B
MURHB840CTT4G	MURS310T3	MZ4099	MZ5525B
MURHB860CTT4G	MURS320T3	MZ4100	MZ5526B
MURHD560T4G	MURS320T3G	MZ4101	MZ5527B
MURHD560W1T4G	MURS340T3	MZ4102	MZ5528B
MURHF860CTG	MURS340T3G	MZ4103	MZ5529B
MURHS160T3G	MURS360BT3G	MZ4104	MZ5530B
MURS105T3G	MURS360-E3/57T	MZ4614	MZPY10
MURS110T3	MURS360T3	MZ4615	MZPY100

Multisim 14.1 Education Components

MZPY11	MZPY62	NBRD5H100T4G	NC7S32_3V
MZPY12	MZPY68	NBR52H100T3G	NC7S32_4V
MZPY13	MZPY7.5	NC_CONTACT	NC7S32_5V
MZPY15	MZPY75	NC_RELAY_RATED	NC7S32_6V
MZPY16	MZPY8.2	NC7S00_2V	NC7S86_2V
MZPY18	MZPY82	NC7S00_3V	NC7S86_3V
MZPY20	MZPY9.1	NC7S00_4V	NC7S86_4V
MZPY22	MZPY91	NC7S00_5V	NC7S86_5V
MZPY24	N2550-6002RB	NC7S00_6V	NC7S86_6V
MZPY27	NAND13	NC7S02_2V	NC7ST00_5V
MZPY3.9	NAND2	NC7S02_3V	NC7ST02_5V
MZPY30	NAND2	NC7S02_4V	NC7ST04_5V
MZPY33	NAND3	NC7S02_5V	NC7ST08_5V
MZPY36	NAND3	NC7S02_6V	NC7ST32_5V
MZPY39	NAND4	NC7S04_2V	NC7ST86_5V
MZPY4.3	NAND4	NC7S04_3V	NC7SU04_2V
MZPY4.7	NAND5	NC7S04_4V	NC7SU04_3V
MZPY43	NAND5	NC7S04_5V	NC7SU04_4V
MZPY47	NAND6	NC7S04_6V	NC7SU04_5V
MZPY5.1	NAND6	NC7S08_2V	NC7SU04_6V
MZPY5.6	NAND7	NC7S08_3V	NC7SZ00_2V
MZPY51	NAND7	NC7S08_4V	NC7SZ00_3V
MZPY56	NAND8	NC7S08_5V	NC7SZ00_4V
MZPY6.2	NAND8	NC7S08_6V	NC7SZ00_5V
MZPY6.8	NBRB8H100T4G	NC7S32_2V	NC7SZ02_2V

Multisim 14.1 Education Components

NC7SZ02_3V	NC7SZ32_4V	NCP1011ST100T3G	NCP1014ST100T3G
NC7SZ02_4V	NC7SZ32_5V	NCP1011ST130T3G	NCP1014ST65T3G
NC7SZ02_5V	NC7SZ38_2V	NCP1011ST65T3G	NCP1027P065G
NC7SZ04_2V	NC7SZ38_3V	NCP1012AP065G	NCP1027P100G
NC7SZ04_3V	NC7SZ38_4V	NCP1012AP100G	NCP1028P065G
NC7SZ04_4V	NC7SZ38_5V	NCP1012AP133G	NCP1028P100G
NC7SZ04_5V	NC7SZ86_2V	NCP1012APL065R2 G	NCP1028PL100R2G
NC7SZ05_2V	NC7SZ86_3V	NCP1012APL100R2 G	NCP1030DMR2G
NC7SZ05_3V	NC7SZ86_4V	NCP1012APL130R2 G	NCP1031DR2G
NC7SZ05_4V	NC7SZ86_5V	NCP1012APL130R2 G	NCP1031MNTXG
NC7SZ05_5V	NC7SZU04_2V	NCP1012ST100T3G	NCP1050P100G
NC7SZ08_2V	NC7SZU04_3V	NCP1012ST130T3G	NCP1050P136G
NC7SZ08_3V	NC7SZU04_4V	NCP1012ST65T3G	NCP1050P44G
NC7SZ08_4V	NC7SZU04_5V	NCP1013AP065G	NCP1050ST100T3G
NC7SZ08_5V	NCP1010AP065G	NCP1013AP100G	NCP1050ST136T3G
NC7SZ125_2V	NCP1010AP100G	NCP1013AP133G	NCP1050ST44T3G
NC7SZ125_3V	NCP1010AP130G	NCP1013ST100T3G	NCP1051P100G
NC7SZ125_4V	NCP1010ST100T3G	NCP1013ST130T3G	NCP1051P136G
NC7SZ125_5V	NCP1010ST130T3G	NCP1013ST65T3G	NCP1051P44G
NC7SZ126_2V	NCP1011AP065G	NCP1014AP065G	NCP1051ST100T3G
NC7SZ126_3V	NCP1011AP100G	NCP1014AP100G	NCP1051ST136T3G
NC7SZ126_4V	NCP1011AP130G	NCP1014APL065R2 G	NCP1051ST44T3G
NC7SZ126_5V	NCP1011APL065R2 G	NCP1014APL100R2 G	NCP1052P100G
NC7SZ32_2V	NCP1011APL130R2 G		NCP1052P136G
NC7SZ32_3V			NCP1052P44G

Multisim 14.1 Education Components

NCP1052ST100T3G	NCP1117DT18G	NCP1117ST50T3G	NCP1216D65R2G
NCP1052ST136T3G	NCP1117DT18RKG	NCP1117STAT3G	NCP1216P100G
NCP1052ST44T3G	NCP1117DT18T5G	NCP1200D100R2G	NCP1216P133G
NCP1053P100G	NCP1117DT20G	NCP1200D40R2G	NCP1216P65G
NCP1053P136G	NCP1117DT20RKG	NCP1200D60R2G	NCP1217AD100R2G
NCP1053P44G	NCP1117DT25G	NCP1200P100G	NCP1217AD133R2G
NCP1053ST100T3G	NCP1117DT25RKG	NCP1200P40G	NCP1217AD65R2G
NCP1053ST136T3G	NCP1117DT25T5G	NCP1200P60G	NCP1217AP100G
NCP1053ST44T3G	NCP1117DT285G	NCP1203D100R2G	NCP1217AP133G
NCP1054P100G	NCP1117DT285RKG	NCP1203D40R2G	NCP1217AP65G
NCP1054P136G	NCP1117DT33G	NCP1203D60R2G	NCP1217D100R2G
NCP1054P44G	NCP1117DT33RKG	NCP1203P100G	NCP1217D133R2G
NCP1054ST100T3G	NCP1117DT33T5G	NCP1203P40G	NCP1217D65R2G
NCP1054ST136T3G	NCP1117DT50G	NCP1203P60G	NCP1217P100G
NCP1054ST44T3G	NCP1117DT50RKG	NCP1207ADR2G	NCP1217P133G
NCP1055P100G	NCP1117DTAG	NCP1207APG	NCP1217P65G
NCP1055P136G	NCP1117DTARKG	NCP1207BDR2G	NCP1230D100R2G
NCP1055P44G	NCP1117DTAT5G	NCP1216AD100R2G	NCP1230D133R2G
NCP1055ST100T3G	NCP1117ST12T3G	NCP1216AD133R2G	NCP1230D165R2G
NCP1055ST136T3G	NCP1117ST15T3G	NCP1216AD65R2G	NCP1230D65R2G
NCP1055ST44T3G	NCP1117ST18T3G	NCP1216AP100G	NCP1230P100G
NCP1117DT12G	NCP1117ST20T3G	NCP1216AP133G	NCP1230P133G
NCP1117DT12RKG	NCP1117ST25T3G	NCP1216AP65G	NCP1230P65G
NCP1117DT15G	NCP1117ST285T3G	NCP1216D100R2G	NCP1271D100R2G
NCP1117DT15RKG	NCP1117ST33T3G	NCP1216D133R2G	NCP1271D65R2G

Multisim 14.1 Education Components

NCP1271P100G	NCP2890DMR2G	NCS2001SN1T1G	NCV1117ST33T3G
NCP1271P65G	NCP4894DMR2G	NCS2001SN2T1G	NCV1117ST50T3G
NCP1308DR2G	NCP4894FCT1G	NCS2001SQ1T2G	NCV1117STAT3G
NCP1337DR2G	NCP4894MNR2G	NCS2001SQ2T2G	NCV2001SN2T1G
NCP1337PG	NCP511SN15T1G	NCS2200SN1T1G	NCV2001SQ2T2G
NCP1338DR2G	NCP511SN18T1G	NCS2200SN2T1G	NCV2901DR2G
NCP1351ADR2G	NCP511SN25T1G	NCS2200SQ2T2G	NCV2901DTBR2G
NCP1351APG	NCP511SN27T1G	NCS2200SQT1G	NCV2902DR2G
NCP1351BDR2G	NCP511SN28T1G	NCS2202SN1T1G	NCV2902DTBR2G
NCP1351BPG	NCP511SN30T1G	NCS2202SN2T1G	NCV2903DMR2G
NCP1351CDR2G	NCP511SN33T1G	NCS2202SQ1T2G	NCV2903DR2G
NCP1351CPG	NCP511SN50T1G	NCS2202SQ2T2G	NCV2904DMR2G
NCP1351DDR2G	NCP5208DR2G	NCV1117DT15RKG	NCV2904DR2G
NCP1351DPG	NCP5217AMNTXG	NCV1117DT18RKG	NCV33063AVDR2G
NCP1377BD1R2G	NCP5355D	NCV1117DT18T5G	NCV33074ADTBR2G
NCP1377BDR2G	NCP5355DG	NCV1117DT20RKG	G
NCP1377BPG	NCP5355PDR2	NCV1117DT25RKG	NCV33074DR2G
NCP1377D1R2G	NCP6334BMTAATB	NCV1117DT33T5G	NCV33272ADR2G
NCP1377DR2G	G	NCV1117DT50RKG	NCV4274CDS33R4G
NCP1377PG	NCP6334CMTAATB	NCV1117DTARKG	NCV4274CDS50R4G
	G		NCV4274CDT33RKG
NCP1410DMR2G	NCR401T	NCV1117ST12T3G	
NCP2809ADMR2G	NCR401U	NCV1117ST15T3G	NCV4274CDT50RKG
NCP2809BDMR2G	NCR402T	NCV1117ST18T3G	NCV833DR2G
NCP2809BMUTXG	NCR402U	NCV1117ST20T3G	NCV890100
NCP2890AFCT2G	NCR405U	NCV1117ST25T3G	NCV890101

Multisim 14.1 Education Components

NCV890103	NDD05N50ZT4G	NDF10N62ZG	NDS9955
NCV890104	NDD60N360U1-1G	NDF11N50ZG	NDS9956A
NCV890130	NDD60N360U1-35G	NDF11N50ZH	NDS9958
NCV890131	NDD60N360U1T4G	NDF9406	NDS9959
NCV896530	NDDP010N25AZ-1H	NDF9407	NDT01N60T1G
NDBA100N10BT4H	NDDP010N25AZT4	NDF9409	NDUL03N150CG
NDBA170N06AT4H	H	NDF9410	NDUL09N150CG
NDBA180N10BT4H	NDF02N60ZG	NDFP03N150CG	NE5532AI
NDD01N60-1G	NDF02N60ZH	NDFPD1N150CG	NE5532AIP
NDD01N60T4G	NDF03N60ZG	NDPL070N10BG	NE5532AP
NDD02N40-1G	NDF03N60ZH	NDPL100N10BG	NE5532IP
NDD02N40T4G	NDF04N60ZG	NDPL180N10BG	NE5532P
NDD02N60Z-1G	NDF04N60ZH	NDS8852H	NE5534AD
NDD02N60ZT4G	NDF04N62ZG	NDS8858H	NE5534AP
NDD03N50Z-1G	NDF05N50ZG	NDS8936	NE5534D
NDD03N50ZT4G	NDF05N50ZH	NDS8947	NE5534P
NDD03N60Z-1G	NDF06N60ZG	NDS9936	NET_10
NDD03N60ZT4G	NDF06N60ZH	NDS9942	NET_12
NDD03N80Z-1G	NDF06N62ZG	NDS9943	NET_14
NDD03N80ZT4G	NDF08N50ZG	NDS9947	NET_16
NDD04N50Z-1G	NDF08N50ZH	NDS9948	NET_18
NDD04N50ZT4G	NDF08N60ZG	NDS9952	NET_2
NDD04N60Z-1G	NDF08N60ZH	NDS9952A	NET_20
NDD04N60ZT4G	NDF10N60ZG	NDS9953	NET_3
NDD05N50Z-1G	NDF10N60ZH	NDS9953A	NET_4

Multisim 14.1 Education Components

NET_6	NHPV15S600G	NI_sbRIO_J7_PORT S	NI-AT-GPIB/TNT
NET_8	NI_2VHDCI_68_68_ RA	NI_sbRIO_P2_CON N	NID9N05CLT4G
NF5101	NI_50MIL_68_RA	NI_sbRIO_P2_PORT S	NI-DAQCard-6024E
NF5102	NI_50MIL_68_V	NI_sbRIO_P3_CON N	NI-DAQCard-6036E
NF5103	NI_cRIO_4LED_RA	NI_sbRIO_P3_PORT S	NI-DAQCard-6062E
NF5301	NI_cRIO_BNC	NI_sbRIO_P4_CON N	NI-DAQPad- 6015(Mass.Term.)
NGB18N40CLBT4G	NI_cRIO_DSUB25M	NI_sbRIO_P4_PORT S	NI-DAQPad-6020E
NGB8207NT4G	NI_cRIO_DSUB37M	NI_sbRIO_P5_CON N	NI-DAQPad-6052E
NGD15N41CLT4G	NI_cRIO_INTERFAC E_GENERIC	NI_sbRIO_P5_PORT S	NI-ExpressCard- GPIB
NGD18N40CLBT4G	NI_cRIO_INTERFAC E_ID	NI_VHDCI_68_RA	NIF9N05CLT1G
NGD8201NT4G	NI_cRIO_INTERFAC E_PARALLEL	NI_VHDCI_68_V	NIF9N05CLT3G
NGTB03N60R2DT4 G	NI_cRIO_INTERFAC E_SPI	NI-78xxR_RDIO	NI-GPIB-ENET/100
NGTB05N60R2DT4 G	NI_cRIO_INTERFAC E_USER	NI-9683_AI	NI-GPIB-ENET/1000
NGTB10N60R2DT4 G	NI_cRIO_SCREWTE RM10	NI-9683_AIO	NI-GPIB-PCII/IIA
NGTB15N60R2FG	NI_MyDAQ_Rail_lef t	NI-9683_DI	NI-GPIB-RS232
NGTB15N60S1EG	NI_MyDAQ_top	NI-9683_DO	NI-GPIB-RS485/422
NGTB20N60L2TF1G	NI_sbRIO_J5_CONN	NI-9683_LVTTL	NI-GPIB-USB-HS
NGTB30N60L2WG	NI_sbRIO_J6_CONN		NI-myDAQ
NGTB50N60FLWG	NI_sbRIO_J7_CONN		NI-PCI-6011E
NGTG20N60L2TF1G			NI-PCI-6013
NHPJ08S600G			NI-PCI-6014
NHPJ15S600G			NI-PCI-6023E
NHPV08S600G			NI-PCI-6024E
			NI-PCI-6030E

Multisim 14.1 Education Components

NI-PCI-6032E	NI-PCI-6233	NI-PCle-6341	NI-PXI-6070E
NI-PCI-6034E	NI-PCI-6236	NI-PCle-6343	NI-PXI-6115
NI-PCI-6035E	NI-PCI-6238	NI-PCle-6351	NI-PXI-6120
NI-PCI-6036E	NI-PCI-6239	NI-PCle-6353	NI-PXI-6122
NI-PCI-6040E	NI-PCI-6250	NI-PCle-6361	NI-PXI-6123
NI-PCI-6052E	NI-PCI-6254	NI-PCle-6363	NI-PXI-6132
NI-PCI-6070E	NI-PCI-6255	NI-PCle- 7841R_RMIO	NI-PXI-6133
NI-PCI-6110	NI-PCI-6259		NI-PXI-6143
NI-PCI-6111	NI-PCI-6280	NI-PCle- 7842R_RMIO	NI-PXI-6221
NI-PCI-6115	NI-PCI-6281	NI-PCle-	NI-PXI-6224
NI-PCI-6120	NI-PCI-6284	7851R_RMIO	NI-PXI-6225
NI-PCI-6122	NI-PCI-6289	NI-PCle- 7852R_RMIO	NI-PXI-6229
NI-PCI-6123	NI-PCI-7811R		NI-PXI-6230
NI-PCI-6132	NI-PCI-7813R	NI-PCle-GPIB	NI-PXI-6232
NI-PCI-6133	NI-PCI- 7830R_RMIO	NI-PCle-GPIB/LP	NI-PXI-6233
NI-PCI-6143		NI-PCle-GPIB+	NI-PXI-6236
NI-PCI-6154	NI-PCI- 7831R_RMIO	NI-PCle-GPIB+/LP	NI-PXI-6238
NI-PCI-6220	NI-PCI-	NI-PCI-GPIB	NI-PXI-6239
NI-PCI-6221	7833R_RMIO	NI-PCI-GPIB/LP	NI-PXI-6250
NI-PCI-6221(37-Pin)	NI-PCI-8232	NI-PCI-GPIB+	NI-PXI-6251
NI-PCI-6224	NI-PCle-6251	NI-PCMCIA-GPIB	NI-PXI-6254
NI-PCI-6225	NI-PCle-6259	NI-PMC-GPIB	NI-PXI-6255
NI-PCI-6229	NI-PCle-6320	NI-PXI-6030E	NI-PXI-6259
NI-PCI-6230	NI-PCle-6321	NI-PXI-6040E	NI-PXI-6280
NI-PCI-6232	NI-PCle-6323	NI-PXI-6052E	NI-PXI-6281

Multisim 14.1 Education Components

NI-PXI-6284	NI-sbRIO-9651	NI-USB-6251(Mass.Term.)	NJL4302D
NI-PXI-6289	NI-SCXI-1127_1-Wire	NI-USB-6255(Mass.Term.)	NJL4302DG
NI-PXI-7811R	NI-SCXI-1127_2-Wire	NI-USB-6259(Mass.Term.)	NJM022BD
NI-PXI-7813R	NI-SCXI-1127_4-Wire	NI-USB-6281(Mass.Term.)	NJM022BL
NI-PXI-7830R_RMIO	NI-SCXI-1127_Independent	NI-USB-6289(Mass.Term.)	NJM022BM
NI-PXI-7831R_RMIO	NI-SCXI-1127_Matrix	NI-USB-7845R_MIO	NJM022D
NI-PXI-7833R_RMIO	NI-SCXI-1128_1-Wire	NI-USB-7846R_MIO	NJM022L
NI-PXI-7841R_RMIO	NI-SCXI-1128_2-Wire	NI-USB-7855R_MIO	NJM022M
NI-PXI-7842R_RMIO	NI-SCXI-1128_4-Wire	NI-USB-7856R_MIO	NJM022V
NI-PXI-7851R_RMIO	NI-SCXI-1128_Independent	NI-USB-78xxR_DIO	NJM062D
NI-PXI-7852R_RMIO	NI-SCXI-1128_Matrix	NJD1718T4G	NJM062L
NI-PXI-7853R_RMIO	NI-SCXI-1160	NJD2873T4G	NJM062M
NI-PXI-7854R_RMIO	NI-SCXI-1163R	NJD35N04G	NJM062V
NI-PXI-8232	NI-USB-6212(Mass.Term.)	NJD35N04T4G	NJM064D
NI-PXIe-6124	NI-USB-6216(Mass.Term.)	NJL0281D	NJM064M
NI-PXIe-6341	NI-USB-6216(Mass.Term.)	NJL0281DG	NJM064V
NI-PXIe-6356	NI-USB-6216(Mass.Term.)	NJL0302D	NJM072BD
NI-PXIe-6358	NI-USB-6216(Mass.Term.)	NJL0302DG	NJM072BL
NI-PXIe-6361	NI-USB-6216(Mass.Term.)	NJL1302DG	NJM072BM
NI-PXIe-6363	NI-USB-6225(Mass.Term.)	NJL3281DG	NJM072BV
NI-PXIe-6366	NI-USB-6225(Mass.Term.)	NJL4281D	NJM072D
NI-PXIe-6368	NI-USB-6225(Mass.Term.)	NJL4281DG	NJM072L
NI-PXI-GPIB	NI-USB-6225(Mass.Term.)	NJL4281DG	NJM072M
NI-sbRIO-9605	NI-USB-6225(Mass.Term.)	NJL4281DG	NJM074D
NI-sbRIO-9606	NI-USB-6225(Mass.Term.)	NJL4281DG	NJM074M
			NJM074V

Multisim 14.1 Education Components

NJM082BD	NJM2059M	NJM2121M	NJM3415M
NJM082BL	NJM2060D	NJM2900M	NJM3416V
NJM082BM	NJM2060M	NJM2900N	NJM353D
NJM082BV	NJM2068D	NJM2902M	NJM353M
NJM082D	NJM2068L	NJM2902N	NJM3900M
NJM082L	NJM2068M	NJM2902V	NJM3900N
NJM082V	NJM2082D	NJM2904D	NJM4250D
NJM084D	NJM2082L	NJM2904L	NJM4250M
NJM084M	NJM2082M	NJM2904M	NJM4565D
NJM084V	NJM2097M	NJM2904V	NJM4565L
NJM13600D	NJM2100D	NJM318D	NJM4565M
NJM13600M	NJM2100L	NJM318M	NJM4565V
NJM13700D	NJM2100M	NJM324D	NJM4580D
NJM13700M	NJM2100V	NJM324M	NJM4580E
NJM1458D	NJM2107F	NJM3403AD	NJM4580L
NJM1458M	NJM2114D	NJM3403AM	NJM4741D
NJM2041D	NJM2114L	NJM3403AV	NJM4741M
NJM2041L	NJM2115D	NJM3404AD	NJM5532D
NJM2041M	NJM2115L	NJM3404AL	NJM5532L
NJM2043D	NJM2115M	NJM3404AM	NJM5532M
NJM2043L	NJM2120D	NJM3414D	NJM5534D
NJM2043M	NJM2120L	NJM3414L	NJM5534M
NJM2058D	NJM2120M	NJM3414M	NJM741D
NJM2058M	NJM2121D	NJM3415D	NJM741E
NJM2059D	NJM2121L	NJM3415L	NJM741M

Multisim 14.1 Education Components

NJMOP-07D	NJVMJD350T4G	NON_IDEAL_BATTE RY	NPD5564
NJMOP-07M	NJVMJD42CRLG		NPD5565
NJT4030PT1G	NJVMJD42CT4G	NON_IDEAL_CAPAC ITOR	NPD5566
NJT4030PT3G	NJVMJD44E3T4G	NON_IDEAL_INDUC TOR	NPD8301
NJT4031NT1G	NJVMJD44H11G		NPD8303
NJT4031NT3G	NJVMJD44H11RLG	NON_IDEAL_RESIST OR	NRVA4004T3G
NJV4030PT1G	NJVMJD44H11T4G	NONC_RELAY_RATE D	NRVB0530T1G
NJV4030PT3G	NJVMJD45H11RLG		NRVB0530T3G
NJV4031NT1G	NJVMJD45H11T4G	NONLINEAR_DEPEN DENT	NRVB0540T1G
NJV4031NT3G	NJVMJD50T4G		NRVB0540T3G
NJVMJB41CT4G	NJVMJD6039T4G	NOR2	NRVB10100G
NJVMJB42CT4G	NJVNJD2873T4G	NOR2	NRVB10100MFST1 G
NJVMJB44H11T4G	NJVNJD35N04G	NOR3	NRVB10100MFST3 G
NJVMJB45H11T4G	NJVNJD35N04T4G	NOR3	
NJVMJD112T4G	NJW0281G	NOR4	NRVB1045MFST1G
NJVMJD117T4G	NJW0302G	NOR4	NRVB1045MFST3G
NJVMJD210T4G	NJW1302G	NOR5	NRVB120ESFT1G
NJVMJD243T4G	NJW21193G	NOR5	NRVB120ESFT3G
NJVMJD253T4G	NJW21194G	NOR6	NRVB120LSFT1G
NJVMJD2955T4G	NJW3281G	NOR6	NRVB1240MFST1G
NJVMJD3055T4G	NJX1675PDR2G	NOR7	NRVB1240MFST3G
NJVMJD31T4G	NLT_VIRTUAL	NOR7	NRVB130T1G
NJVMJD32CG	NMOSFET_Thermal	NOR8	NRVB140ESFT1G
NJVMJD32CT4G	NO_CONTACT	NOR8	NRVB140ESFT3G
NJVMJD32T4G	NO_RELAY_RATED	NOT	NRVB140SFT1G

Multisim 14.1 Education Components

NRVB140SFT3G	NRVB8H100MFST1 G	NRVBD640CTT4G	NRVTS1045EMFST1 G
NRVB1H100SFT3G		NRVBD650CTT4G	
NRVB2045EMFST1 G	NRVB8H100MFST3 G	NRVBD660CTG	NRVTS1045EMFST3 G
NRVB2045EMFST3 G	NRVBA130LT3G	NRVBD660CTT4G	NRVTS1260EMFST1 G
NRVB2H100SFT3G	NRVBA160T3G	NRVBM110ET1G	
NRVB30H100MFST 1G	NRVBA1H100T3G	NRVBM110LT1G	NRVTS1260EMFST3 G
NRVB30H100MFST 3G	NRVBA210LT3G	NRVBM110LT3G	
	NRVBA2H100T3G	NRVBM120ET1G	NRVTS1545EMFST1 G
NRVB440MFST1G	NRVBA340T3G	NRVBM120ET3G	NRVTS1545EMFST3 G
NRVB440MFST3G	NRVBB1060T4G	NRVBM130LT1G	
NRVB440MFSWFT1 G	NRVBB20100CTT4G	NRVBM130LT3G	NRVTS245ESFT1G
NRVB440MFSWFT3 G	NRVBB2060CTT4G	NRVBM140T1G	NRVTS245ESFT3G
	NRVBB20H100CTT4 G	NRVBM140T3G	NRVTS260ESFT1G
NRVB460MFST1G		NRVBS2040LT3G	NRVTS260ESFT3G
NRVB460MFST3G	NRVBB2535CTLG	NRVBS240LT3G	NRVTS560EMFST1G
NRVB5100MFST1G	NRVBB2535CTLT4G	NRVBS260T3G	NRVTS560EMFST3G
NRVB5100MFST3G	NRVBB3030CTLG	NRVBS3100T3G	NRVTS860EMFST1G
NRVB540MFST1G	NRVBB3030CTLT4G	NRVBS3200T3G	NRVTS860EMFST3G
NRVB540MFST3G	NRVBB30H60CTT4G	NRVBS3201T3G	NRVTS44100ET3G
NRVB560MFST1G	NRVBB4030T4G	NRVBS330T3G	NRVTS44100ET3G
NRVB560MFST3G	NRVBB41H100CTT4 G	NRVBS360T3G	NRVTS44100ET3G
NRVB5H100MFST1 G	NRVBBS20100CTT4 G	NRVBS4201T3G	NRVTS44100ET3G
	NRVBD1035CTLT4G	NRVBS540T3G	NRVTS44100ET3G
	NRVBD640CTG	NRVS1504T3G	NRVTS44100ET3G

Multisim 14.1 Education Components

NRVUB1620CTT4G	NSBA123JF3T5G	NSBC114EPDXV6T5G	NSBC124EDP6T5G
NRVUB1660CTT4G	NSBA123TDP6T5G	NSBC114TDP6T5G	NSBC124EDXV6T1G
NRVUD550PFT4G	NSBA123TF3T5G	NSBC114TDXV6T1G	NSBC124EF3T5G
NRVUD620CTG	NSBA124EDP6T5G	NSBC114TF3T5G	NSBC124EPDXV6T1G
NRVUD620CTT4G	NSBA124EF3T5G	NSBC114YDP6T5G	NSBC124XF3T5G
NRVUS230T3G	NSBA124XF3T5G	NSBC114YDXV6T1G	NSBC143EDP6T5G
NRVUS240T3G	NSBA143EDP6T5G	NSBC114YDXV6T5G	NSBC143EF3T5G
NSA5.0AT3G	NSBA143EF3T5G	NSBC114YF3T5G	NSBC143TF3T5G
NSB12ANT3G	NSBA143TF3T5G	NSBC114YPDP6T5G	NSBC143TPDXV6T1G
NSB4904DW1T1G	NSBA143ZDP6T5G	NSBC114YPDXV6T1G	NSBC143ZDP6T5G
NSB8MT-E3/81	NSBA143ZF3T5G	NSBC114YPDXV6T5G	NSBC143ZDXV6T1G
NSB9435T1G	NSBA144EDP6T5G	NSBC115EDXV6T1G	NSBC143ZF3T5G
NSBA114EDP6T5G	NSBA144EDXV6T1G	NSBC115TDP6T5G	NSBC143ZPDP6T5G
NSBA114EDXV6T1G	NSBA144EF3T5G	NSBC115TF3T5G	NSBC143ZPDXV6T1G
NSBA114EF3T5G	NSBA144TF3T5G	NSBC115TPDP6T5G	NSBC144EDP6T5G
NSBA114TDP6T5G	NSBA144WDP6T5G	NSBC123EF3T5G	NSBC144EDXV6T1G
NSBA114TF3T5G	NSBA144WF3T5G	NSBC123JDP6T5G	NSBC144EDXV6T5G
NSBA114YDP6T5G	NSBC113EF3T5G	NSBC123JF3T5G	NSBC144EF3T5G
NSBA114YDXV6T1G	NSBC114EDP6T5G	NSBC123JPDP6T5G	NSBC144EPDP6T5G
NSBA115EDXV6T1G	NSBC114EDXV6T1G	NSBC123JPDXV6T1G	NSBC144EPDXV6T1G
NSBA115TDP6T5G	NSBC114EDXV6T5G	NSBC123TF3T5G	NSBC144TF3T5G
NSBA115TF3T5G	NSBC114EF3T5G	NSBC123TDP6T5G	NSBC144WDP6T5G
NSBA123EF3T5G	NSBC114EPDP6T5G		
NSBA123JDP6T5G	NSBC114EPDXV6T1G		
NSBA123JDXV6T5G			

Multisim 14.1 Education Components

NSBC144WF3T5G	NSIC2020BT3G	NSR0340HT1G	NSR20F30NXT5G
NSD16F3T5G	NSIC2030BT3G	NSR0340P2T5G	NSR30CM3T5G
NSD914F3T5G	NSIC2050BT3G	NSR0340V2T1G	NSRLV20MW2T1G
NSDEMP11XV6T1G	NSL12AWT1G	NSR0520V2T1G	NSS12100M3T5G
NSDEMP11XV6T5G	NSM80100MT1G	NSR05F20NXT5G	NSS12100UW3TCG
NSI45015WT1G	NSM80101MT1G	NSR05F30NXT5G	NSS12100XV6T1G
NSI45020AT1G	NSPM1041BMUTB G	NSR05F40NXT5G	NSS12200LT1G
NSI45020JZT1G	NSR0130P2T5G	NSR05T40P2T5G	NSS12200WT1G
NSI45020T1G	NSR0140P2T5G	NSR05T40XV2T5G	NSS12201LT1G
NSI45025AT1G	NSR01F30MXT5G	NSR0620P2T5G	NSS12500UW3T2G
NSI45025AZT1G	NSR01F30NXT5G	NSR1020MW2T1G	NSS12501UW3T2G
NSI45025T1G	NSR01L30MXT5G	NSR1020MW2T3G	NSS12601CF8T1G
NSI45025ZT1G	NSR01L30NXT5G	NSR10404NXT5G	NSS1C200LT1G
NSI45030AT1G	NSR0230P2T5G	NSR10F20NXT5G	NSS1C200MZ4T1G
NSI45030AZT1G	NSR0240HT1G	NSR10F30NXT5G	NSS1C200MZ4T3G
NSI45030T1G	NSR0240P2T5G	NSR10F40NXT5G	NSS1C201LT1G
NSI45030ZT1G	NSR0240V2T1G	NSR15304NXT5G	NSS1C201MZ4T1G
NSI45035JZT1G	NSR02F30MXT5G	NSR15405NXT5G	NSS1C201MZ4T3G
NSI45060DDT4G	NSR02F30NXT5G	NSR15406NXT5G	NSS1C300ET4G
NSI45090DDT4G	NSR02L30NXT5G	NSR20204NXT5G	NSS1C301ET4G
NSI45090JDT4G	NSR0320MW2T1G	NSR20206NXT5G	NSS20200LT1G
NSI50010YT1G	NSR0320MW2T3G	NSR20305NXT5G	NSS20201LT1G
NSI50150ADT4G	NSR0320XV6T1G	NSR20306NXT5G	NSS20300MR6T1G
NSI50350ADT4G	NSR0320XV6T5G	NSR20406NXT5G	NSS20500UW3T2G
NSI50350AST3G		NSR20F20NXT5G	NSS20501UW3T2G

Multisim 14.1 Education Components

NSS20601CF8T1G	NST30010MXV6T1G	NSV60100DMTWTB G	NSVMMBTH10LT1G
NSS30100LT1G			NSVMMUN2132LT1G
NSS30101LT1G	NST3904DXV6T1G	NSV60101DMTWTB G	
NSS30201MR6T1G	NST3904DXV6T5G		NSVMMUN2232LT1G
NSS35200CF8T1G	NST3904F3T5G	NSV60600MZ4T1G	G
NSS35200MR6T1G	NST3906DXV6T1G	NSV60600MZ4T3G	NSVMUN2212T1G
NSS40200LT1G	NST3906F3T5G	NSV60601MZ4T1G	NSVMUN2233T1G
NSS40200UW6T1G	NST3946DXV6T1G	NSV60601MZ4T3G	NSVMUN5131T1G
NSS40201LT1G	NST3946DXV6T5G	NSV9435T1G	NSVMUN5132T1G
NSS40300DDR2G	NST846BF3T5G	NSVB123JPDV6T1G	NSVMUN5212DW1T1G
NSS40300MDR2G	NST847BF3T5G	NSVB143ZPDV6T1G	NSVMUN5314DW1T3G
NSS40300MZ4T1G	NST848BF3T5G		
NSS40301MDR2G	NST856BF3T5G	NSVB144EPDV6T1G	NSVMUN5333DW1T1G
NSS40301MZ4T1G	NST857BF3T5G		
NSS40302PDR2G	NSTB1005DXV5T1G	NSVBA114YDV6T1G	NSVMUN5334DW1T1G
NSS40500UW3T2G	NSTR4501NT1G	NSVBAT54LT1G	NSVT30010MXV6T1G
NSS40501UW3T2G	NSV1C300ET4G	NSVBAT54WT1G	G
NSS40600CF8T1G	NSV1C301ET4G	NSVBAV70TT1G	NSVT3904DXV6T1G
NSS40601CF8T1G	NSV20200LT1G	NSVBAV70TT3G	NSVT65010MW6T1G
NSS60100DMTTBG	NSV20201LT1G	NSVBC124EDV6T1G	G
NSS60101DMTTBG	NSV40200LT1G		NSVT65011MW6T1G
NSS60200LT1G	NSV40201LT1G	NSVBBCP56-10T3G	NTA4001NT1G
NSS60201LT1G	NSV40300MDR2G	NSVBBCP69T1G	NTA4151PT1G
NSS60600MZ4T1G	NSV40300MZ4T1G	NSVJ3557SA3T1G	NTA4153NT1G
NSS60601MZ4T1G	NSV40301MZ4T1G	NSVMMBD353LT1G	NTA7002NT1G
		NSVMMBT589LT1G	

Multisim 14.1 Education Components

NTB25P06T4G	NTCLE100E3102GB 0	NTCLE100E3152GB 0	NTCLE100E3222GB 0
NTB30N06LT4G			
NTB30N20T4G	NTCLE100E3102HB 0	NTCLE100E3152HB 0	NTCLE100E3222HB 0
NTB45N06LT4G	NTCLE100E3102JB0	NTCLE100E3152JB0	NTCLE100E3222JB0
NTB45N06T4G	NTCLE100E3103GB 0	NTCLE100E3153GB 0	NTCLE100E3223GB 0
NTB5404NT4G			
NTB5405NT4G	NTCLE100E3103HB 0	NTCLE100E3153HB 0	NTCLE100E3223HB 0
NTB5605PT4G	NTCLE100E3103JB0	NTCLE100E3153JB0	NTCLE100E3223JB0
NTB60N06T4G	NTCLE100E3104GB 0	NTCLE100E3154GB 0	NTCLE100E3224GB 0
NTB6410ANG			
NTB6410ANT4G	NTCLE100E3104HB 0	NTCLE100E3154HB 0	NTCLE100E3224HB 0
NTB6411ANG	NTCLE100E3104JB0	NTCLE100E3154JB0	NTCLE100E3224JB0
NTB6411ANT4G			
NTB6412ANG	NTCLE100E3109GB 0	NTCLE100E3159GB 0	NTCLE100E3229GB 0
NTB6412ANT4G	NTCLE100E3109HB 0	NTCLE100E3159HB 0	NTCLE100E3229HB 0
NTB6413ANG			
NTB6413ANT4G	NTCLE100E3109JB0	NTCLE100E3159JB0	NTCLE100E3229JB0
NTB75N03L09T4G	NTCLE100E3123GB 0	NTCLE100E3202GB 0	NTCLE100E3272GB 0
NTB75N06T4G	NTCLE100E3123HB 0	NTCLE100E3202HB 0	NTCLE100E3272HB 0
NTBV5605T4G			
NTCLE100E3101GB 0	NTCLE100E3123JB0	NTCLE100E3202JB0	NTCLE100E3272JB0
NTCLE100E3101HB 0	NTCLE100E3151GB 0	NTCLE100E3221GB 0	NTCLE100E3331GB 0
NTCLE100E3101JB0	NTCLE100E3151HB 0	NTCLE100E3221HB 0	NTCLE100E3331HB 0
	NTCLE100E3151JB0	NTCLE100E3221JB0	NTCLE100E3331JB0

Multisim 14.1 Education Components

NTCLE100E3332GB 0	NTCLE100E3472GB 0	NTCLE100E3503GB 0	NTCLE101E3103SB0 NTCLE101E3104SB0
NTCLE100E3332HB 0	NTCLE100E3472HB 0	NTCLE100E3503HB 0	NTCLE101E3472SB0
NTCLE100E3332JB0	NTCLE100E3472JB0	NTCLE100E3503JB0	NTCLE101E3473SB0
NTCLE100E3333GB 0	NTCLE100E3473GB 0	NTCLE100E3681GB 0	NTCLE101E3502SB0 NTCLE101E3602SB0
NTCLE100E3333HB 0	NTCLE100E3473HB 0	NTCLE100E3681HB 0	NTCLE101E3682SB0 NTCLE101E3802SB0
NTCLE100E3333JB0	NTCLE100E3473JB0	NTCLE100E3681JB0	NTCLE101E3C90172 NTCLE101E3C90173
NTCLE100E3334GB 0	NTCLE100E3474GB 0	NTCLE100E3682GB 0	NTCLE203E3103FB0 NTCLE203E3103GB
NTCLE100E3334HB 0	NTCLE100E3474HB 0	NTCLE100E3682HB 0	0
NTCLE100E3334JB0	NTCLE100E3474JB0	NTCLE100E3682JB0	NTCLE203E3103HB 0
NTCLE100E3338GB 0	NTCLE100E3478GB 0	NTCLE100E3683GB 0	NTCLE203E3103JB0 NTCLE203E3104FB0
NTCLE100E3338HB 0	NTCLE100E3478HB 0	NTCLE100E3683HB 0	NTCLE203E3104GB 0
NTCLE100E3338JB0	NTCLE100E3478JB0	NTCLE100E3683JB0	NTCLE203E3104HB 0
NTCLE100E3339GB 0	NTCLE100E3479GB 0	NTCLE100E3688GB 0	NTCLE203E3104JB0 NTCLE203E3123FB0
NTCLE100E3339HB 0	NTCLE100E3479HB 0	NTCLE100E3688HB 0	NTCLE203E3123GB 0
NTCLE100E3339JB0	NTCLE100E3479JB0	NTCLE100E3688JB0	NTCLE203E3123HB 0
NTCLE100E3471GB 0	NTCLE100E3502GB 0	NTCLE100E3689GB 0	
NTCLE100E3471HB 0	NTCLE100E3502HB 0	NTCLE100E3689HB 0	
NTCLE100E3471JB0	NTCLE100E3502JB0	NTCLE100E3689JB0	

Multisim 14.1 Education Components

NTCLE203E3123JB0	NTCLE203E3472HB 0	NTCLE213E3103FLB 0	NTCLE213E3212FM B0
NTCLE203E3202FB0	NTCLE203E3472JB0	NTCLE213E3103GH B0	NTCLE213E3212GM B0
NTCLE203E3202GB 0	NTCLE203E3473FB0	NTCLE213E3103GL B0	NTCLE213E3212HM B0
NTCLE203E3202HB 0	NTCLE203E3473GB 0	NTCLE213E3103HH B0	NTCLE213E3212JM B0
NTCLE203E3202JB0	NTCLE203E3473HB 0	NTCLE213E3103HL B0	NTCLE213E3303FH B0
NTCLE203E3222FB0	NTCLE203E3473JB0	NTCLE213E3103JHB 0	NTCLE213E3303GH B0
NTCLE203E3222GB 0	NTCLE203E3474FB0	NTCLE213E3103JLB 0	NTCLE213E3303HH B0
NTCLE203E3222HB 0	NTCLE203E3474GB 0	NTCLE213E3104FXB 0	NTCLE213E3303JHB 0
NTCLE203E3222JB0	NTCLE203E3474HB 0	NTCLE213E3104GX B0	NTCS0402E3103FH T
NTCLE203E3223FB0	NTCLE203E3474JB0	NTCLE213E3104HX B0	NTCS0402E3103FLT T
NTCLE203E3223GB 0	NTCLE203E3502FB0	NTCLE213E3104JXB 0	NTCS0402E3103GL T
NTCLE203E3223HB 0	NTCLE203E3502GB 0	NTCLE213E3123FM B0	NTCS0402E3103HH T
NTCLE203E3223JB0	NTCLE203E3502HB 0	NTCLE213E3123GM B0	NTCS0402E3103HL T
NTCLE203E3272FB0	NTCLE203E3502JB0	NTCLE213E3123HM B0	NTCS0402E3103JHT T
NTCLE203E3272GB 0	NTCLE203E3683FB0	NTCLE213E3123JM B0	NTCS0402E3103JLT T
NTCLE203E3272HB 0	NTCLE203E3683GB 0		
NTCLE203E3272JB0	NTCLE203E3683HB 0		
NTCLE203E3472FB0	NTCLE203E3683JB0		
NTCLE203E3472GB 0	NTCLE213E3103FH B0		

Multisim 14.1 Education Components

NTCS0402E3104FH T	NTCS0402E3333FM T	NTCS0402E3683FH T	NTCS0603E3104GX T
NTCS0402E3104GH T	NTCS0402E3333GM T	NTCS0402E3683GH T	NTCS0603E3104HX T
NTCS0402E3104HH T	NTCS0402E3333HM T	NTCS0402E3683HH T	NTCS0603E3104JXT T
NTCS0402E3104JHT T	NTCS0402E3333JM T	NTCS0402E3683JHT T	NTCS0603E3124FM T
NTCS0402E3153FH T	NTCS0402E3472FM T	NTCS0603E3103FH T	NTCS0603E3124GM T
NTCS0402E3153GH T	NTCS0402E3472GM T	NTCS0603E3103FLT T	NTCS0603E3124HM T
NTCS0402E3153HH T	NTCS0402E3472HM T	NTCS0603E3103FM T	NTCS0603E3124JM T
NTCS0402E3153JHT T	NTCS0402E3472JM T	NTCS0603E3103GH T	NTCS0603E3153FM T
NTCS0402E3214FM T	NTCS0402E3473FXT T	NTCS0603E3103GL T	NTCS0603E3153GM T
NTCS0402E3214GM T	NTCS0402E3473GX T	NTCS0603E3103GM T	NTCS0603E3153HM T
NTCS0402E3214HM T	NTCS0402E3473HX T	NTCS0603E3103HH T	NTCS0603E3153JM T
NTCS0402E3214JM T	NTCS0402E3473JXT T	NTCS0603E3103HL T	NTCS0603E3202FLT T
NTCS0402E3223FM T	NTCS0402E3474FH T	NTCS0603E3103HM T	NTCS0603E3202GL T
NTCS0402E3223GM T	NTCS0402E3474GH T	NTCS0603E3103JHT T	NTCS0603E3202HL T
NTCS0402E3223HM T	NTCS0402E3474HH T	NTCS0603E3103JLT T	NTCS0603E3202JLT T
NTCS0402E3223JM T	NTCS0402E3474JHT T	NTCS0603E3104FXT T	NTCS0603E3222FM T

Multisim 14.1 Education Components

NTCS0603E3222GM T	NTCS0603E3472GH T	NTCS0805E3103HH T	NTCS0805E3153JM T
NTCS0603E3222HM T	NTCS0603E3472HH T	NTCS0805E3103HL T	NTCS0805E3222FM T
NTCS0603E3222JM T	NTCS0603E3472JHT T	NTCS0805E3103HM T	NTCS0805E3222GM T
NTCS0603E3223FM T	NTCS0603E3473FH T	NTCS0805E3103JHT T	NTCS0805E3222HM T
NTCS0603E3223GM T	NTCS0603E3473GH T	NTCS0805E3103JLT T	NTCS0805E3222JM T
NTCS0603E3223HM T	NTCS0603E3473HH T	NTCS0805E3103JM T	NTCS0805E3223FH T
NTCS0603E3223JM T	NTCS0603E3473JHT T	NTCS0805E3104FM T	NTCS0805E3223GH T
NTCS0603E3272FM T	NTCS0603E3683FH T	NTCS0805E3104FXT T	NTCS0805E3223HH T
NTCS0603E3272GM T	NTCS0603E3683GH T	NTCS0805E3104GM T	NTCS0805E3223JHT T
NTCS0603E3272HM T	NTCS0603E3683HH T	NTCS0805E3104GX T	NTCS0805E3223JHT T
NTCS0603E3272JM T	NTCS0603E3683JHT T	NTCS0805E3104HM T	NTCS0805E3333FH T
NTCS0603E3333FH T	NTCS0805E3103FH T	NTCS0805E3104HX T	NTCS0805E3333GH T
NTCS0603E3333GH T	NTCS0805E3103FLT T	NTCS0805E3104JM T	NTCS0805E3333HH T
NTCS0603E3333HH T	NTCS0805E3103FM T	NTCS0805E3104JXT T	NTCS0805E3333JHT T
NTCS0603E3333JHT T	NTCS0805E3103GH T	NTCS0805E3153FM T	NTCS0805E3334FH T
NTCS0603E3472FH T	NTCS0805E3103GL T	NTCS0805E3153GM T	NTCS0805E3334GH T
	NTCS0805E3103GM T	NTCS0805E3153HM T	NTCS0805E3334HH T

Multisim 14.1 Education Components

NTCS0805E3334JHT	NTCS0805E3684GX T	NTD3055L170T4G	NTD4855NT4G
NTCS0805E3472FM T	NTCS0805E3684HX T	NTD32N06LT4G	NTD4856NT4G
NTCS0805E3472GM T	NTCS0805E3684JXT	NTD40N03RT4G	NTD4857NT4G
NTCS0805E3472HM T	NTD110N02RT4G	NTD4302T4G	NTD4858N-35G
NTCS0805E3472JM T	NTD12N10-1G	NTD4804NT4G	NTD4858NT4G
NTCS0805E3473FH T	NTD12N10T4G	NTD4805N-1G	NTD4860N-35G
NTCS0805E3473GH T	NTD14N03RT4G	NTD4805NT4G	NTD4860NT4G
NTCS0805E3473HH T	NTD18N06LT4G	NTD4806N-35G	NTD4863N-35G
NTCS0805E3473JHT	NTD18N06T4G	NTD4806NT4G	NTD4863NAT4G
NTCS0805E3474FXT	NTD20N03L27T4G	NTD4808N-1G	NTD4863NT4G
NTCS0805E3474GX T	NTD20N06T4G	NTD4808NT4G	NTD4863NT4H
NTCS0805E3474HX T	NTD20N06T4G	NTD4809N-35G	NTD4865NT4G
NTCS0805E3474JXT	NTD20P06LG	NTD4809NH-1G	NTD4904N-1G
NTCS0805E3683FXT	NTD20P06LT4G	NTD4809NH-35G	NTD4904N-35G
NTCS0805E3683GX T	NTD24N06LT4G	NTD4809NHT4G	NTD4904NT4G
NTCS0805E3683HX T	NTD24N06T4G	NTD4809NT4G	NTD4905N-1G
NTCS0805E3683JXT	NTD2955-1G	NTD4810N-35G	NTD4905N-35G
NTCS0805E3684FXT	NTD2955G	NTD4810NT4G	NTD4905NT4G
	NTD2955T4G	NTD4813N-35G	NTD4906N-1G
	NTD3055-094-1G	NTD4813NH-1G	NTD4906N-35G
	NTD3055-094T4G	NTD4813NH-35G	NTD4906NT4G
	NTD3055-150T4G	NTD4813NHT4G	NTD4909N-1G
	NTD3055L104-1G	NTD4813NT4G	NTD4909N-35G
	NTD3055L104G	NTD4815N-35G	NTD4909NT4G
	NTD3055L104T4G	NTD4815NT4G	NTD4910N-1G

Multisim 14.1 Education Components

NTD4910N-35G	NTD5805NT4G	NTF3055L108T1G	NTHD4508NT1G
NTD4910NT4G	NTD5806NT4G	NTF3055L175T1G	NTHD4P02FT1G
NTD4913N-1G	NTD5807NT4G	NTF5P03T3G	NTHS4101PT1G
NTD4913N-35G	NTD5865NL-1G	NTF6P02T3G	NTHS4166NT1G
NTD4913NT4G	NTD5865NLT4G	NTGD1100LT1G	NTHS5404T1G
NTD4960N-1G	NTD5867NL-1G	NTGD3149CT1G	NTHS5441T1G
NTD4960N-35G	NTD5867NLT4G	NTGD4161PT1G	NTHS5443T1G
NTD4960NT4G	NTD6414AN-1G	NTGD4167CT1G	NTJD1155LT1G
NTD4963N-1G	NTD6414ANT4G	NTGS3130NT1G	NTJD4001NT1G
NTD4963N-35G	NTD6415AN-1G	NTGS3136PT1G	NTJD4105CT1G
NTD4963NT4G	NTD6415ANLT4G	NTGS3441PT1G	NTJD4105CT2G
NTD4965N-1G	NTD6415ANT4G	NTGS3441T1G	NTJD4152PT1G
NTD4965N-35G	NTD6416AN-1G	NTGS3443T1G	NTJD4158CT1G
NTD4965NT4G	NTD6416ANL-1G	NTGS3446T1G	NTJD4158CT2G
NTD4969N-1G	NTD6416ANLT4G	NTGS4111PT1G	NTJD4401NT1G
NTD4969N-35G	NTD6416ANT4G	NTGS4141NT1G	NTJD5121NT1G
NTD4969NT4G	NTD6600NT4G	NTGS5120PT1G	NTJD5121NT2G
NTD4970N-1G	NTD70N03R-1G	NTHC5513T1G	NTJS3151PT1G
NTD4970N-35G	NTD70N03RT4G	NTHD2102PT1G	NTJS3157NT1G
NTD4970NT4G	NTDV20N06T4G	NTHD3100CT1G	NTJS4151PT1G
NTD5406NT4G	NTE4151PT1G	NTHD3101FT1G	NTJS4160NT1G
NTD5407NT4G	NTE4153NT1G	NTHD3102CT1G	NTJS4405NT1G
NTD5802NT4G	NTF2955T1G	NTHD3133PFT1G	NTK3043NT1G
NTD5803NT4G	NTF3055-100T1G	NTHD4102PT1G	NTK3134NT1G
NTD5804NT4G	NTF3055-100T3G	NTHD4502NT1G	NTK3134NT5G

Multisim 14.1 Education Components

NTK3139PT1G	NTMD4184PFR2G	NTMFS4835NT1G	NTMFS4923NET3G
NTK3139PT5G	NTMD4820NR2G	NTMFS4836NT1G	NTMFS4925NET1G
NTK3142PT1G	NTMD4840NR2G	NTMFS4837NHT1G	NTMFS4925NET3G
NTLGD3502NT2G	NTMD4884NFR2G	NTMFS4839NHT1G	NTMFS4925NT1G
NTLGF3402PT2G	NTMD4N03R2G	NTMFS4841NHT1G	NTMFS4925NT3G
NTLJD3115PT1G	NTMD5836NLR2G	NTMFS4841NT1G	NTMFS4926NET1G
NTLJD3119CTAG	NTMD5838NLR2G	NTMFS4845NT1G	NTMFS4926NET3G
NTLJD3119CTBG	NTMD6N02R2G	NTMFS4846NT1G	NTMFS4926NT1G
NTLJD4116NT1G	NTMD6N04R2G	NTMFS4847NAT1G	NTMFS4926NT3G
NTLJF3117PT1G	NTMD6P02R2G	NTMFS4847NAT3G	NTMFS4927NT1G
NTLJF4156NT1G	NTMFD4901NFT1G	NTMFS4847NT1G	NTMFS4927NT3G
NTLJF4156NTAG	NTMFD4901NFT3G	NTMFS4851NT1G	NTMFS4931NT1G
NTLJS2103PTBG	NTMFD4902NFT1G	NTMFS4852NT1G	NTMFS4931NT3G
NTLJS3113PT1G	NTMFD4902NFT3G	NTMFS4852NT3G	NTMFS4934NT1G
NTLJS3113PTAG	NTMFS4108NT1G	NTMFS4897NFT1G	NTMFS4934NT3G
NTLJS4114NT1G	NTMFS4119NT1G	NTMFS4897NFT3G	NTMFS4935NT1G
NTLLD4901NFTWG	NTMFS4744NT1G	NTMFS4898NFT1G	NTMFS4935NT3G
NTLUD3A260PZTAG	NTMFS4821NT1G	NTMFS4898NFT3G	NTMFS4936NT1G
NTLUD3A260PZTBG	NTMFS4823NT1G	NTMFS4899NFT1G	NTMFS4936NT3G
NTLUF4189NZTAG	NTMFS4823NT3G	NTMFS4899NFT3G	NTMFS4937NT1G
NTLUS3A40PZTAG	NTMFS4825NFET1G	NTMFS4921NT1G	NTMFS4937NT3G
NTLUS3A40PZTBG	NTMFS4825NFET3G	NTMFS4921NT3G	NTMFS4939NT1G
NTLUS3A90PZTAG	NTMFS4833NT1G	NTMFS4922NET1G	NTMFS4939NT3G
NTLUS3A90PZTBG	NTMFS4833NT3G	NTMFS4922NET3G	NTMFS4941NT1G
NTMD3P03R2G	NTMFS4834NT1G	NTMFS4923NET1G	NTMFS4941NT3G

Multisim 14.1 Education Components

NTMFS4943NT1G	NTMS4937NR2G	NTS1045MFST3G	NTSB30100S-1G
NTMFS4943NT3G	NTMS4939NR2G	NTS1260MFST1G	NTSB30U100CT-1G
NTMFS4945NT1G	NTMS5835NLR2G	NTS1260MFST3G	NTSJ20100CTG
NTMFS4983NFT1G	NTMS5838NLR2G	NTS1545MFST1G	NTSJ2080CTG
NTMFS4983NFT3G	NTMS5P02R2G	NTS1545MFST3G	NTSJ20U100CTG
NTMFS4985NFT1G	NTNS3A65PZT5G	NTS2101PT1G	NTSJ30100CTG
NTMFS4985NFT3G	NTNUS3171PZT5G	NTS245SFT1G	NTSJ3080CTG
NTMFS5830NLT1G	NTP2955G	NTS245SFT3G	NTSJ30U80CTG
NTMFS5832NLT1G	NTP35N15G	NTS260SFT1G	NTSS3100T3G
NTMS10P02R2G	NTR0202PLT1G	NTS260SFT3G	NTSS5100T3G
NTMS4176PR2G	NTR1P02LT1G	NTS4001NT1G	NTST20100CTG
NTMS4177PR2G	NTR1P02LT3G	NTS4101PT1G	NTST20120CTG
NTMS4503NR2G	NTR2101PT1G	NTS4173PT1G	NTST20U100CTG
NTMS4800NR2G	NTR3161NT1G	NTS4409NT1G	NTST30100CTG
NTMS4801NR2G	NTR3162PT1G	NTS560MFST1G	NTST30100CTH
NTMS4802NR2G	NTR4003NT1G	NTS560MFST3G	NTST30100SG
NTMS4807NR2G	NTR4003NT3G	NTS860MFST1G	NTST30120CTG
NTMS4816NR2G	NTR4101PT1G	NTS860MFST3G	NTST30U100CTG
NTMS4840NR2G	NTR4170NT1G	NTSA4100T3G	NTST30U100CTH
NTMS4872NR2G	NTR4171PT1G	NTSAF345T3G	NTST40120CTG
NTMS4873NFR2G	NTR4501NT1G	NTSAF5100T3G	NTST40120CTH
NTMS4916NR2G	NTR4502PT1G	NTSAF545T3G	NTSV20100CTG
NTMS4917NR2G	NTR4502PT3G	NTSB20100CT-1G	NTSV20120CTG
NTMS4920NR2G	NTR4503NT1G	NTSB20U100CT-1G	NTSV20U100CTG
NTMS4935NR2G	NTS1045MFST1G	NTSB30100CT-1G	NTSV30100CTG

Multisim 14.1 Education Components

NTSV30120CTG	NTTFS4C06NTAG	NTZD3152PT1G	NUF4001MUT2G
NTTD4401FR2G	NTTFS4C06NTWG	NTZD3154NT1G	NUF4220MNT1G
NTTFS4800NTAG	NTTFS4C08NTAG	NTZD3154NT2G	NUF4401MNT1G
NTTFS4821NTAG	NTTFS4C08NTWG	NTZD3154NT5G	NUF4403MNT1G
NTTFS4821NTWG	NTTFS4C10NTAG	NTZD3155CT1G	NUF6001MUT2G
NTTFS4823NTAG	NTTFS4C10NTWG	NTZD3155CT2G	NUF6105FCT1G
NTTFS4823NTWG	NTTFS4C13NTAG	NTZD3155CT5G	NUF6401MNT1G
NTTFS4824NTAG	NTTFS4C13NTWG	NTZD5110NT1G	NUF6402MNT1G
NTTFS4840NTAG	NTTFS5811NLTAG	NTZS3151PT1G	NUF8001MUT2G
NTTFS4929NTAG	NTTFS5811NLTWG	NUD3105DMT1G	NUF8401MNT4G
NTTFS4929NTWG	NTTFS5820NLTAG	NUD3105LT1G	NUF8402MNT4G
NTTFS4932NTAG	NTTFS5820NLTWG	NUD3112DMT1G	NUF8410MNT4G
NTTFS4932NTWG	NTTFS5C453NLTAG	NUD3112LT1G	NUF9002FCT1G
NTTFS4937NTAG	NTTFS5C453NLTWG	NUD3124DMT1G	NUMERIC_KEYPAD_ 4X4
NTTFS4937NTWG	NTTFS5C454NLTAG	NUD3124LT1G	NUMERIC_KEYPAD_ 4X5
NTTFS4939NTAG	NTTFS5C454NLTWG	NUD3160DMT1G	
NTTFS4939NTWG	NTTFS5C670NLTAG	NUD3160LT1G	NUP1105LT1G
NTTFS4941NTAG	NTTFS5C670NLTWG	NUF2042XV6T1G	NUP1301
NTTFS4941NTWG	NTTFS5C673NLTAG	NUF2114MNT1G	NUP1301ML3T1G
NTTFS4943NTAG	NTTFS5C673NLTWG	NUF2116MNT1G	NUP1301U
NTTFS4945NTAG	NTUD3127CT5G	NUF2221W1T2G	NUP2105LT1G
NTTFS4985NFTAG	NTUD3128NT5G	NUF2230XV6T1G	NUP2202W1T2G
NTTFS4985NFTWG	NTUD3169CZT5G	NUF2450MUT2G	NUP4102XV6T1G
NTTFS4C05NTAG	NTUD3170NZT5G	NUF3101FCT1G	NUP4103FCT1G
NTTFS4C05NTWG	NTUD3171PZT5G	NUF3102MUTAG	NUP4201DR2G

Multisim 14.1 Education Components

NUP4201MR6T1G	NVF2955T1G	NVMFD5877NLWFT 1G	NVMFS5C450NLT1 G
NUP4202W1T2G	NVF3055-100T1G		
NUP4301MR6T1G	NVF3055L108T1G	NVMFD5877NLWFT 3G	NVMFS5C450NLT3 G
NUP4302MR6T1G	NVF3055L108T3G	NVMFS5826NLT1G	NVMFS5C450NLWF T1G
NUP4304MR6T1G	NVF5P03T3G	NVMFS5826NLT3G	
NUP45V6P5T5G	NVF6P02T3G	NVMFS5832NLT1G	NVMFS5C450NLWF T3G
NUS3116MTR2G	NVMD3P03R2G	NVMFS5834NLT1G	NVMS4816NR2G
NVATS5A106PLZT4 G	NVMFD5485NLT1G	NVMFS5834NLT3G	NVR5198NLT1G
	NVMFD5485NLT3G	NVMFS5844NLT1G	NVR5198NLT3G
NVATS5A112PLZT4 G	NVMFD5485NLWFT 1G	NVMFS5844NLT3G	NVTA7002NT1G
	NVMFD5485NLWFT 3G	NVMFS5885NLT1G	NVTFS4824NTAG
NVATS5A113PLZT4 G		NVMFS5885NLT3G	NVTFS4824NTWG
NVATS5A304PLZT4 G	NVMFD5489NLT1G	NVMFS5C404NT1G	NVTFS4C25NTAG
	NVMFD5489NLT3G	NVMFS5C404NT3G	NVTFS5116PLTAG
NVB6413ANT4G		NVMFS5C404NWFT 1G	NVTFS5116PLTWG
NVC3S5A51PLZT1G	NVMFD5489NLWFT 1G		
	NVMFD5489NLWFT 3G	NVMFS5C404NWFT 3G	NVTFS5124PLTAG
NVD4804NT4G			NVTFS5124PLTWG
NVD5117PLT4G	NVMFD5852NLT1G	NVMFS5C430NLT1 G	NVTFS5826NLTAG
NVD5802NT4G	NVMFD5852NLWFT 1G		NVTFS5826NLTWG
NVD5807NT4G		NVMFS5C430NLT3 G	
NVD5865NLT4G	NVMFD5873NLT1G		NVTJD4001NT1G
NVD5890NT4G	NVMFD5873NLWFT 1G	NVMFS5C430NLWF T1G	NVTR01P02LT1G
NVD6415ANLT4G			NVTR0202PLT1G
NVD6824NLT4G	NVMFD5877NLT1G	NVMFS5C430NLWF T3G	NVTR4502PT1G
NVDD5894NLT4G	NVMFD5877NLT3G		NVTR4503NT1G

Multisim 14.1 Education Components

NX2301P	NZH11C	NZL5V6AXV3T1G	NZX18A
NX3008NBK	NZH12B	NZL6V8AXV3T1G	NZX18B
NX3008NBKMB	NZH13B	NZL7V5AXV3T1G	NZX18C
NX3008NBKS	NZH15B	NZQA5V6XV5T1G	NZX20A
NX3008NBKT	NZH16C	NZQA6V8AXV5T1G	NZX20B
NX3008NBKV	NZH18C	NZQA6V8AXV5T2G	NZX22A
NX3008NBKW	NZH20C	NZQA6V8AXV5T3G	NZX22B
NX3008PBK	NZH22C	NZX10A	NZX24A
NX3008PBKMB	NZH24C	NZX10C	NZX24B
NX3008PBKS	NZH27C	NZX11A	NZX27A
NX3008PBKT	NZH30C	NZX11C	NZX27B
NX3008PBKV	NZH3V0B	NZX11D	NZX27C
NX3008PBKW	NZH3V3A	NZX12A	NZX2V4A
NX7002AK	NZH3V6B	NZX12B	NZX2V7B
NX7002AKS	NZH3V9B	NZX12C	NZX30A
NX7002AKW	NZH4V3B	NZX12D	NZX30C
NX7002BK	NZH4V7B	NZX13B	NZX33C
NXP3875G	NZH5V1B	NZX13C	NZX36C
NXP3875Y	NZH5V6B	NZX14A	NZX3V0B
NZ9F2V4ST5G	NZH6V2B	NZX14B	NZX3V3B
NZ9F2V4T5G	NZH6V8B	NZX14C	NZX3V3C
NZ9F2V7ST5G	NZH7V5C	NZX15B	NZX3V6C
NZ9F5V1T5G	NZH8V2B	NZX16A	NZX3V9C
NZ9F6V2ST5G	NZH9V1B	NZX16B	NZX4V3C
NZH10C	NZL5V6ATT1G	NZX16C	NZX4V7A

Multisim 14.1 Education Components

NZX4V7C	OCTAL_REG	OP05AH	OP07AZ
NZX4V7D	OHN3019U	OP05AJ	OP07CD
NZX5V1B	OHN3030U	OP05AJ8	OP07CH
NZX5V1C	OHN3040U	OP05AZ	OP07CJ8
NZX5V1D	OHN3075U	OP05CH	OP07CJG
NZX5V6A	OHN3113U	OP05CJ	OP07CN8
NZX5V6B	OHN3119U	OP05CJ8	OP07CP
NZX5V6C	OHN3175U	OP05CN8	OP07CS8
NZX5V6D	OHS3019U	OP05CP	OP07DD
NZX5V6E	OHS3030U	OP05CZ	OP07DJG
NZX6V2B	OHS3040U	OP05EH	OP07DP
NZX6V2C	OHS3075U	OP05EJ	OP07ED
NZX6V2D	OHS3119U	OP05EJ8	OP07EH
NZX6V2E	OHS3175U	OP05EN8	OP07EJ8
NZX6V8A	OL	OP05EP	OP07EJG
NZX6V8B	OP01CZ	OP05EZ	OP07EN8
NZX6V8C	OP01J	OP05H	OP07EP
NZX7V5A	OP02AJ	OP05J	OP07H
NZX7V5B	OP02AZ	OP05J8	OP07J
NZX7V5D	OP02CJ	OP06AJ	OP07J8
NZX8V2A	OP02CP	OP06GJ	OP07RC/883
NZX8V2B	OP02CZ	OP06GZ	OP07Y
NZX8V2D	OP04AK	OP07AH	OP07Z
NZX9V1B	OP04AY	OP07AJ	OP08
NZX9V1E	OP04EY	OP07AJ8	OP09AY

Multisim 14.1 Education Components

OP09BY	OP15EJ	OP16C	OP177GS
OP10AY	OP15EZ	OP16CH	OP177GZ
OP10CY	OP15FH	OP16EH	OP183GP
OP10EY	OP15FJ	OP16EJ	OP183GS
OP10Y	OP15FP	OP16EZ	OP184ES
OP113EP	OP15FZ	OP16FH	OP191GP
OP113ES	OP15GH	OP16FJ	OP191GS
OP113FP	OP15GJ	OP16FP	OP193EP
OP113FS	OP15GN8	OP16FZ	OP193ES
OP1177AR	OP15GP	OP16GH	OP193FP
OP1177ARM	OP15GS	OP16GJ	OP193FS
OP11GP	OP15GZ	OP16GN8	OP196GP
OP11GS	OP160ARC/883	OP16GP	OP196GS
OP12BJ	OP160AZ	OP16GS	OP200AZ
OP12BZ/883	OP160FZ	OP16GZ	OP200EZ
OP12EJ	OP160GP	OP176GP	OP200FZ
OP12EZ	OP160GS	OP176GS	OP200GP
OP15AH	OP162DRU	OP177AZ	OP200GS
OP15AJ	OP162GS	OP177BRC/883	OP207AY
OP15AZ	OP162GSZ	OP177BZ	OP207EY
OP15BH	OP16AH	OP177EZ	OP207FY
OP15BJ/883	OP16AJ	OP177FP	OP20BJ
OP15BZ/883	OP16BH	OP177FS	OP20BZ
OP15CH	OP16BJ/883	OP177FZ	OP20CZ
OP15EH	OP16BZ/883	OP177GP	OP20FP

Multisim 14.1 Education Components

OP20GJ	OP215EJ	OP21GP	OP227GJ
OP20GP	OP215EJ8	OP21HS	OP227GN
OP20GZ	OP215EN8	OP220AJ	OP22AJ/883
OP20HJ	OP215EP	OP220AZ	OP22AZ
OP20HS	OP215EZ	OP220CJ	OP22HP
OP20HZ	OP215FJ	OP220CZ	OP22HS
OP213AZ/883	OP215FP	OP220EZ	OP22HZ
OP213BZ/883	OP215FZ	OP220FZ	OP237AJ
OP213EP	OP215GH	OP220GJ	OP237CJ
OP213ES	OP215GJ8	OP220GP	OP237EJ
OP213EZ	OP215GN8	OP220GS	OP237EN
OP213FP	OP215GP	OP220GZ	OP237GJ
OP213FS	OP215GS	OP221AJ/883	OP237GN
OP215AH	OP215GZ	OP221AZ	OP249AJ
OP215AJ	OP2177AR	OP221BJ	OP249ARC/883
OP215AJ8	OP2177ARM	OP221CJ	OP249AZ
OP215AZ	OP2177ARMZ	OP221EZ	OP249EJ
OP215BJ/883	OP2177ARZ	OP221GJ	OP249FJ
OP215BRC/883	OP21AJ	OP221GP	OP249FZ
OP215BZ/883	OP21AZ	OP221GS	OP249GP
OP215CH	OP21EZ	OP221GZ	OP249GPZ
OP215CJ/883	OP21FJ	OP227AJ	OP249GS
OP215CJ8	OP21FP	OP227CJ	OP249GSZ
OP215CZ/883	OP21FZ	OP227EJ	OP260AJ
OP215EH	OP21GJ	OP227EN	OP260ARC/883

Multisim 14.1 Education Components

OP260GP	OP27CH	OP281GRU	OP293FP
OP260GS	OP27CJ	OP281GS	OP293FS
OP262DRU	OP27CJ8	OP282AZ/883	OP295A
OP262DRUZ-REEL	OP27CJG	OP282GP	OP295AP
OP262GS	OP27CZ	OP282GS	OP295GP
OP262GSZ	OP27EH	OP283GP	OP295GS
OP262HRUZ-REEL	OP27EJ	OP283GS	OP296GP
OP270EZ	OP27EJ8	OP284EP	OP296GS
OP270FZ	OP27EN8	OP284ES	OP296HRU
OP270GP	OP27EP	OP284FP	OP297ARC/883
OP270GS	OP27EPZ	OP284FS	OP297AZ
OP275GP	OP27EZ	OP285GP	OP297AZ/883
OP275GS	OP27FJ	OP285GS	OP297EZ
OP279GP	OP27FP	OP290ARC/883	OP297FP
OP279GS	OP27FZ	OP290AZ	OP297FZ
OP279HRU	OP27GH	OP290EZ	OP297GP
OP27AH	OP27GJ	OP290FZ	OP297GS
OP27AJ	OP27GJ8	OP290GP	OP32AZ
OP27AJ8	OP27GJZ	OP290GS	OP32EP
OP27AJG	OP27GN8	OP291GP	OP32EZ
OP27AL	OP27GP	OP291GS	OP32FP
OP27AZ	OP27GPZ	OP292GP	OP32FZ
OP27BJ	OP27GS	OP292GS	OP32GP
OP27BR/883	OP27GSZ	OP293EP	OP32GZ
OP27BZ	OP27GZ	OP293ES	OP37AFK

Multisim 14.1 Education Components

OP37AH	OP37GJ	OP41EJ	OP42AZ
OP37AJ	OP37GJ8	OP41FJ	OP42EJ
OP37AJ8	OP37GN8	OP41GP	OP42EZ
OP37AJG	OP37GP	OP41GS	OP42FJ
OP37AL	OP37GS	OP420BY	OP42FZ
OP37AZ	OP37GZ	OP420CRC/883	OP42GP
OP37BJ	OP400ATC/883	OP420CY	OP42GS
OP37BRC/883	OP400AY	OP420FY	OP43
OP37BZ	OP400EY	OP420GP	OP43A
OP37CH	OP400FY	OP420GS	OP43B
OP37CJ	OP400GP	OP420GY	OP43E
OP37CJ8	OP400GS	OP420HP	OP43F
OP37CJG	OP400HP	OP420HS	OP43G
OP37CZ	OP400HS	OP420HY	OP44AJ
OP37EH	OP413EP	OP421BY	OP462DRU
OP37EJ	OP413ES	OP421CY	OP462DRUZ-REEL
OP37EJ8	OP413EY	OP421FY	OP462DS
OP37EN8	OP413FP	OP421GP	OP462GS
OP37EP	OP413FS	OP421GS	OP462GSZ
OP37EPZ	OP4177AR	OP421GY	OP462HRU-REEL
OP37EZ	OP4177ARU	OP421HP	OP462HRUZ-REEL
OP37FJ	OP4177ARUZ	OP421HS	OP467ARC/883
OP37FP	OP4177ARZ	OP421HY	OP467AY/883
OP37FZ	OP41AJ	OP42AJ	OP467GP
OP37GH	OP41BJ	OP42ARC/883	OP467GS

Multisim 14.1 Education Components

OP470ARC/883	OP491GSZ	OP50EY	OP77GP
OP470ATC/883	OP492GP	OP50FY	OP77GS
OP470AY	OP492GS	OP61ARC/883	OP80BJ
OP470EY	OP493EP	OP61AZ	OP80EJ
OP470GP	OP493ES	OP61FZ	OP80FJ
OP470GS	OP493FP	OP61GP	OP80GP
OP481GRU	OP493FS	OP61GS	OP80GS
OP481GS	OP495GP	OP64AJ	OP906
OP482ARC/883	OP495GS	OP64ARC/883	OP90ARC/883
OP482AY/883	OP495GSZ	OP64AZ	OP90AZ
OP482GP	OP496GP	OP64GP	OP90EZ
OP482GPZ	OP496GS	OP64GS	OP90FZ
OP484EP	OP496HRU	OP727AR	OP90GP
OP484ES	OP497AY	OP727ARU	OP90GS
OP484FP	OP497BRC/883	OP727ARUZ	OP950
OP484FPZ	OP497BY	OP747AR	OP97AJ
OP484FS	OP497CY	OP747ARU	OP97AZ
OP490ATC/883	OP497FP	OP777AR	OP97EP
OP490AY	OP497FS	OP777ARM	OP97FJ
OP490EY	OP497FY	OP77BJ	OP97FP
OP490FY	OP497GP	OP77BRC/883	OP97FS
OP490GP	OP497GS	OP77BZ	OP97FZ
OP490GS	OP497GY	OP77EZ	OP999
OP491GP	OP50AY	OP77FJ	OPA1013CN8
OP491GS	OP50BY	OP77FZ	OPA1013DN8

Multisim 14.1 Education Components

OPA111AM	OPA131UJ	OPA1642AIDR	OPA209AIDR
OPA111BM	OPA132P	OPA1644AID	OPA2107AM
OPA111SM	OPA132PA	OPA1644AIPW	OPA2107AP
OPA121KM	OPA132U	OPA1688ID	OPA2107AU
OPA121KP	OPA132UA	OPA177EZ	OPA2107BM
OPA121KU	OPA134PA	OPA177FP	OPA2107SM
OPA124P	OPA134UA	OPA177FZ	OPA2111AM
OPA124PA	OPA137N	OPA177GP	OPA2111BM
OPA124PB	OPA137NA	OPA177GS	OPA2111KM
OPA124U	OPA137P	OPA177GZ	OPA2111KP
OPA124UA	OPA137PA	OPA180ID	OPA2111SM
OPA124UB	OPA137U	OPA180IDBVR	OPA211AID
OPA128JM	OPA137UA	OPA180IDGKR	OPA211AIDGKR
OPA128KM	OPA140AID	OPA191ID	OPA211AIDR
OPA128LM	OPA140AIDBVR	OPA191IDBVT	OPA211AIDRGR
OPA128SM	OPA140AIDGKR	OPA191IDGKT	OPA211ID
OPA129P	OPA140AIDR	OPA192ID	OPA211IDGKR
OPA129PB	OPA141AIDGKR	OPA192IDBVT	OPA211IDR
OPA129U	OPA141AIDR	OPA192IDGKT	OPA211IDRGR
OPA129UB	OPA1612AID	OPA197ID	OPA2130PA
OPA130PA	OPA1622IDRCT	OPA197IDBVT	OPA2130UA
OPA130UA	OPA1632D	OPA197IDGKT	OPA2131PA
OPA131PA	OPA1632DGN	OPA209AID	OPA2131PJ
OPA131PJ	OPA1642AID	OPA209AIDBVR	OPA2131UA
OPA131UA	OPA1642AIDGKR	OPA209AIDGKR	OPA2131UJ

Multisim 14.1 Education Components

OPA2132P	OPA2234PA	OPA2301AIDR	OPA2342EA
OPA2132PA	OPA2234U	OPA2316SIDGS	OPA2342UA
OPA2132U	OPA2234UA	OPA2317ID	OPA2343EA/250
OPA2132UA	OPA2237EA	OPA2317IDGKR	OPA2343UA
OPA2134PA	OPA2237UA	OPA2330AID	OPA2344EA/250
OPA2134UA	OPA2241PA	OPA2330AIDGKR	OPA2344PA
OPA2137E	OPA2241UA	OPA2330AIDR	OPA2344UA
OPA2137EA	OPA2244EA	OPA2330AIDRBR	OPA2345EA/250
OPA2137P	OPA2244PA	OPA2330AIDRG4	OPA2345UA
OPA2137PA	OPA2244UA	OPA2333AIDGKR	OPA2347EA
OPA2137U	OPA2251PA	OPA2333AIDR	OPA2347UA
OPA2137UA	OPA2251UA	OPA2333AIDRBR	OPA2349EA/250
OPA2140AID	OPA2277P	OPA2333AIDRG4	OPA2349UA
OPA2140AIDGKR	OPA2277PA	OPA2334AIDGSR	OPA234E
OPA2140AIDR	OPA2277U	OPA2335AID	OPA234E/250
OPA2141AIDGKR	OPA2277UA	OPA2335AIDGKR	OPA234EA
OPA2141AIDR	OPA227P	OPA2335AIDR	OPA234EA/250
OPA2209AID	OPA227PA	OPA2337EA/250	OPA234P
OPA2209AIDGKR	OPA227U	OPA2337PA	OPA234PA
OPA2209AIDR	OPA227UA	OPA2337UA	OPA234U
OPA2227P	OPA228P	OPA2338EA/250	OPA234UA
OPA2227PA	OPA228U	OPA2338UA	OPA2350EA
OPA2227U	OPA2300AIDGSR	OPA2340EA	OPA2350PA
OPA2227UA	OPA2301AID	OPA2340PA	OPA2350UA
OPA2234P	OPA2301AIDGKR	OPA2340UA	OPA2353EA/250

Multisim 14.1 Education Components

OPA2353UA	OPA2379AIDG4	OPA2652E	OPA2691I-14D
OPA2354AIDDA	OPA237NA	OPA2652U	OPA2691ID
OPA2354AIDGKR	OPA237UA	OPA2658P	OPA2703EA/250
OPA2355DGSA/250	OPA2380AIDGKR	OPA2658PB	OPA2703PA
OPA2357AIDGSR	OPA2381AIDGKR	OPA2658U	OPA2703UA
OPA2363AIDGSR	OPA2381AIDRBT	OPA2658UB	OPA2704EA/250
OPA2363AIRSVR	OPA241PA	OPA2674I-14D	OPA2704PA
OPA2363IDGSR	OPA241UA	OPA2674ID	OPA2704UA
OPA2369AIDCNR	OPA244NA	OPA2677T	OPA2725AID
OPA2369AIDGKR	OPA244PA	OPA2677U	OPA2725AIDGKR
OPA2373AIDGSR	OPA244UA	OPA2680N	OPA2725AIDR
OPA2373AIDRCR	OPA251PA	OPA2680U	OPA2726AIDGST
OPA2374AID	OPA251UA	OPA2681N	OPA2727AID
OPA2374AIDCNR	OPA2541AM	OPA2681U	OPA2727AIDRBR
OPA2374AIDG4	OPA2541BM	OPA2682N	OPA2727AIDRG4
OPA2376AID	OPA2541SM	OPA2682U	OPA2735AID
OPA2376AIDGKR	OPA2541SMQ	OPA2683ID	OPA2735AIDGKR
OPA2376AIDR	OPA2544T	OPA2683IDCNR	OPA2735AIDR
OPA2376AIYZDR	OPA2604AP	OPA2683IDG4	OPA2743EA/250
OPA2377AID	OPA2604AU	OPA2683IDGST	OPA2743PA
OPA2377AIDGKR	OPA2613ID	OPA2684ID	OPA2743UA
OPA2377AIDR	OPA2613IDTJ	OPA2684IDCNR	OPA277AIDRMR
OPA2378AIDCNR	OPA2614ID	OPA2686U	OPA277P
OPA2379AID	OPA2614IDTJ	OPA2690I-14D	OPA277PA
OPA2379AIDCNR	OPA2626IDGKT	OPA2690ID	OPA277U

Multisim 14.1 Education Components

OPA277UA	OPA2889IDGST	OPA336NA/250	OPA347SA
OPA27AJ	OPA2890IDGST	OPA336NJ/250	OPA347UA
OPA27AZ	OPA300AID	OPA336U	OPA348AID
OPA27BJ	OPA300AIDBV	OPA336UA	OPA348AIDBV
OPA27BZ	OPA301AID	OPA337EA/250	OPA348AIDCKR
OPA27CJ	OPA301AIDBV	OPA337NA/250	OPA349NA
OPA27CZ	OPA316IDBVR	OPA337PA	OPA349SA
OPA27EJ	OPA316IDCKR	OPA337UA	OPA349UA
OPA27EZ	OPA317ID	OPA338NA/250	OPA350EA
OPA27FJ	OPA317IDBVR	OPA338UA	OPA350PA
OPA27FZ	OPA317IDCKR	OPA340NA	OPA350UA
OPA27GJ	OPA320AIDBVR	OPA340PA	OPA353NA
OPA27GP	OPA320SAIDBVR	OPA340UA	OPA353UA
OPA27GU	OPA322AIDBVR	OPA342NA	OPA354AIDBV
OPA27GZ	OPA322SAIDBVR	OPA342PA	OPA354AIDDA
OPA2822E/250	OPA333AID	OPA342UA	OPA355NA
OPA2822U	OPA333AIDBVR	OPA343NA	OPA355QDBVRQ1
OPA2835ID	OPA333AIDCKR	OPA343UA	OPA355UA
OPA2835IDGS	OPA333AIDG4	OPA344NA	OPA356AID
OPA2835IRMCR	OPA334AID	OPA344PA	OPA356AIDBVT
OPA2835IRUNR	OPA335EA/250	OPA344UA	OPA357AIDBV
OPA2836ID	OPA335UA	OPA345NA	OPA3583AM
OPA2836IDGS	OPA335AID	OPA345UA	OPA3583JM
OPA2836IRUNR	OPA335AIDBV	OPA347NA	OPA358AIDCK
OPA2846ID	OPA336N/250	OPA347PA	OPA360AIDCK

Multisim 14.1 Education Components

OPA363ID	OPA377AIDR	OPA404BG	OPA4228PA
OPA363IDBV	OPA378AIDBVR	OPA404KP	OPA4228UA
OPA364ID	OPA378AIDCKR	OPA404KU	OPA4234PA
OPA364IDBV	OPA379AID	OPA404SG	OPA4234U
OPA365AID	OPA379AIDBVR	OPA4130PA	OPA4234UA
OPA365AIDBVR	OPA379AIDCKR	OPA4130UA	OPA4237UA
OPA3680E	OPA379AIDG4	OPA4131NA	OPA4241PA
OPA3680U	OPA37AJ	OPA4131NJ	OPA4241UA
OPA3681E	OPA37AZ	OPA4131PA	OPA4243EA
OPA3681U	OPA37BJ	OPA4131PJ	OPA4244EA
OPA3682E	OPA37BZ	OPA4131UA	OPA4251PA
OPA3682U	OPA37CJ	OPA4132PA	OPA4251UA
OPA3690ID	OPA37CZ	OPA4132UA	OPA4277PA
OPA3690IDBQR	OPA37EJ	OPA4134UA	OPA4277UA
OPA3690IDG4	OPA37EZ	OPA4137P	OPA4317ID
OPA3693IDBQ	OPA37FJ	OPA4137PA	OPA4317IPW
OPA3695IDBQ	OPA37FZ	OPA4137U	OPA4330AID
OPA369AIDCKR	OPA37GJ	OPA4137UA	OPA4330AIPW
OPA373AID	OPA37GP	OPA4140AID	OPA4330AIRGYR
OPA373AIDBV	OPA37GU	OPA4140AIPW	OPA4340EA
OPA374AID	OPA37GZ	OPA4141AID	OPA4340PA
OPA374AIDBV	OPA380AID	OPA4141AIPW	OPA4340UA
OPA377AID	OPA380AIDGK	OPA4209AIPW	OPA4342EA
OPA377AIDBVR	OPA381AIDGK	OPA4227PA	OPA4342PA
OPA377AIDCKR	OPA404AG	OPA4227UA	OPA4342UA

Multisim 14.1 Education Components

OPA4345UA	OPA4703EA/250	OPA548T	OPA602CM
OPA4347EA	OPA4703UA	OPA549S	OPA602SM
OPA4347UA	OPA4704EA/250	OPA549T	OPA603AP
OPA4348AID	OPA4704UA	OPA551FA/500	OPA603AU
OPA4348AIP	OPA4743EA/250	OPA551FAKTWT	OPA604AP
OPA4354AID	OPA4743UA	OPA551PA	OPA604AU
OPA4354AIPWR	OPA4820ID	OPA551UA	OPA606KM
OPA4374AID	OPA4820IPWR	OPA552FA/500	OPA606KP
OPA4374AIPWR	OPA4872ID	OPA552FAKTWT	OPA606LM
OPA4377AIPW	OPA501AM	OPA552PA	OPA620KG
OPA4379AIPWR	OPA501BM	OPA552UA	OPA620KP
OPA445AP	OPA501RM	OPA561PWP	OPA620KU
OPA445BM	OPA501SM	OPA564AIDWD	OPA620LG
OPA445SM	OPA502BM	OPA564AIDWP	OPA620SG
OPA452TA	OPA502SM	OPA567AIRHGR	OPA621KG
OPA454AIDDA	OPA511AM	OPA569AIDWP	OPA621KP
OPA4650P	OPA512BM	OPA600BM	OPA621KU
OPA4650PB	OPA512SM	OPA600CM	OPA621LG
OPA4650U	OPA541AM	OPA600SM	OPA621SG
OPA4658P	OPA541AP	OPA600TM	OPA622AP
OPA4658PB	OPA541BM	OPA602AM	OPA622AU
OPA4658U	OPA541SM	OPA602AP	OPA623AP
OPA4658UB	OPA544F	OPA602AU	OPA623AU
OPA4684ID	OPA544T	OPA602BM	OPA625IDBVR
OPA4684IPWT	OPA547T	OPA602BP	OPA625IDBVT

Multisim 14.1 Education Components

OPA627AM	OPA641UB	OPA650NB	OPA659IDRBR
OPA627AP	OPA642H	OPA650P	OPA671AP
OPA627AU	OPA642HSQ	OPA650PB	OPA675JG
OPA627BM	OPA642P	OPA650U	OPA675KG
OPA627BP	OPA642PB	OPA650UB	OPA675SG
OPA627SM	OPA642U	OPA651N	OPA676JG
OPA628AP	OPA642UB	OPA651NB	OPA676KG
OPA628AU	OPA643H	OPA651P	OPA676SG
OPA633KP	OPA643HSQ	OPA651PB	OPA678AG
OPA637AM	OPA643P	OPA651U	OPA678AP
OPA637AP	OPA643PB	OPA651UB	OPA678AU
OPA637AU	OPA643U	OPA653IDBVR	OPA678SG
OPA637BM	OPA643UB	OPA653IDRBR	OPA680N
OPA637BP	OPA644U	OPA654AM	OPA680P
OPA637SM	OPA644UB	OPA655H	OPA680U
OPA640H	OPA646H	OPA655HSQ	OPA681N
OPA640HSQ	OPA646HSQ	OPA655P	OPA681P
OPA640P	OPA646P	OPA655PB	OPA681U
OPA640U	OPA646PB	OPA655UB	OPA682N
OPA640UB	OPA646U	OPA656N	OPA682P
OPA641H	OPA646UB	OPA656U	OPA682U
OPA641HSQ	OPA648H	OPA658N	OPA683BV
OPA641P	OPA648P	OPA658P	OPA683ID
OPA641PB	OPA648U	OPA658U	OPA684ID
OPA641U	OPA650N	OPA659IDBVR	OPA684IDBV

Multisim 14.1 Education Components

OPA686N	OPA728AIDRBT	OPA857IRGTR	OPS697rx
OPA686U	OPA734AID	OPA860ID	OPS697tx
OPA687N	OPA734AIDBV	OPAMP_3T_VIRTU AL	OPS698rx
OPA687U	OPA735AID		OPS698tx
OPA690ID	OPA735AIDBV	OPAMP_5T_VIRTU AL	OPT301M
OPA690IDBV	OPA743NA	Op-Amp_741	OPTOCOUPLER_VIR TUAL
OPA693ID	OPA743PA	OPAMP_RATED	OR2
OPA693IDBVT	OPA743UA	OPS665rx	OR2
OPA694ID	OPA77EZ	OPS665tx	OR3
OPA694IDBVR	OPA77FP	OPS666rx	OR3
OPA698ID	OPA77FZ	OPS666tx	OR4
OPA699ID	OPA77GP	OPS667rx	OR4
OPA703NA	OPA820ID	OPS667tx	OR5
OPA703PA	OPA820IDBVR	OPS690rx	OR5
OPA703UA	OPA820IDG4	OPS690tx	OR6
OPA704NA	OPA827AID	OPS691rx	OR6
OPA704PA	OPA827AIDGKR	OPS691tx	OR7
OPA704UA	OPA830ID	OPS692rx	OR7
OPA725AID	OPA830IDBVT	OPS692tx	OR8
OPA725AIDBV	OPA835IDBVR	OPS693rx	OR8
OPA726AID	OPA836IDBVR	OPS693tx	OSM910P
OPA726AIDGK	OPA842ID	OPS695rx	OSTV7163151
OPA727AIDGKR	OPA842IDBV	OPS695tx	OSTV7203101
OPA727AIDRBT	OPA847ID	OPS696rx	OSTV7203151
OPA728AIDGKT	OPA847IDBV	OPS696tx	

Multisim 14.1 Education Components

OUTPUT_COIL	P6KE100A-E3/54	P6SMB62AT3G	PA21
OUTPUT_COIL_NEG ATED	P6KE10A-E3/54	P6SMB68AT3G	PA21A
	P6KE200AG	PA01	PA25
OUTPUT_MODULE_ 120Vdc	P6KE200ARLG	PA02	PA25A
OUTPUT_MODULE_ 120Vrms	P6KE6.8AG	PA02A	PA41
	P6KE6.8ARLG	PA03	PA41A
OUTPUT_MODULE_ 12Vdc	P6KE8.2A-E3/54	PA03A	PA41M/883
OUTPUT_MODULE_ 12Vrms	P6KE9.1A-E3/54	PA04	PA45
	P6SMB11CAT3G	PA04A	PA51
OUTPUT_MODULE_ 240Vdc	P6SMB13AT3G	PA05	PA51A
	P6SMB15AT3G	PA05A	PA51M/883
OUTPUT_MODULE_ 240Vrms	P6SMB18AT3G	PA07	PA81J
OUTPUT_MODULE_ 24Vdc	P6SMB20AT3G	PA07A	PA83
	P6SMB22AT3G	PA07M/883	PA83A
OUTPUT_MODULE_ 24Vrms	P6SMB22CAT3G	PA08	PA83M/883
OUTPUT_MODULE_ 5Vdc	P6SMB24A-E3/52	PA08/883	PA84
	P6SMB24AT3G	PA08A	PA84A
OUTPUT_MODULE_ 75Vdc	P6SMB24CA-E3/52	PA09	PA84M/883
	P6SMB24CAT3G	PA09A	PA85
OVERLOAD	P6SMB33A-E3/52	PA10	PA85A
P121	P6SMB33AT3G	PA10A	PA85M
P123	P6SMB36A-E3/52	PA10M/883	PA87
P4KE10CA-E3/54	P6SMB43CAT3G	PA12	PA87A
P4KE300A/3	P6SMB51CAT3G	PA12A	PA88
P4SMA36CA-E3/61	P6SMB6.8AT3G	PA12M/883	PA88A

Multisim 14.1 Education Components

PA89	PBHV9115T	PBLS2023D	PBLS6024D
PA89A	PBHV9115X	PBLS2024D	PBRN113ET
PAR_GEN_CHK	PBHV9115Z	PBLS4001D	PBRN113ZT
PB_DPST	PBHV9215Z	PBLS4001V	PBRN123ET
PB_DPST	PBHV9414Z	PBLS4001Y	PBRN123YT
PB_NC	PBHV9515QA	PBLS4002D	PBRP113ET
PB_NO	PBHV9540Z	PBLS4002V	PBRP113ZT
PB50	PBHV9560Z	PBLS4002Y	PBRP123ET
PB58	PBLS1501V	PBLS4003D	PBRP123YT
PB58A	PBLS1501Y	PBLS4003V	PBSS2515E
PBHV8115T	PBLS1502V	PBLS4003Y	PBSS2515M
PBHV8115X	PBLS1502Y	PBLS4004D	PBSS2515MB
PBHV8115Z	PBLS1503V	PBLS4004V	PBSS2515VPN
PBHV8118T	PBLS1503Y	PBLS4004Y	PBSS2515VS
PBHV8140Z	PBLS1504V	PBLS4005D	PBSS2515YPN
PBHV8215Z	PBLS1504Y	PBLS4005V	PBSS2540E
PBHV8540T	PBLS2001D	PBLS4005Y	PBSS2540M
PBHV8540X	PBLS2001S	PBLS6001D	PBSS2540MB
PBHV8540Z	PBLS2002D	PBLS6002D	PBSS301ND
PBHV8560Z	PBLS2002S	PBLS6003D	PBSS301NX
PBHV9040T	PBLS2003D	PBLS6004D	PBSS301NZ
PBHV9040X	PBLS2003S	PBLS6005D	PBSS301PD
PBHV9040Z	PBLS2004D	PBLS6021D	PBSS301PX
PBHV9050T	PBLS2021D	PBLS6022D	PBSS301PZ
PBHV9050Z	PBLS2022D	PBLS6023D	PBSS302ND

Multisim 14.1 Education Components

PBSS302NX	PBSS306PX	PBSS4032PZ	PBSS4160DS
PBSS302NZ	PBSS306PZ	PBSS4032SN	PBSS4160PAN
PBSS302PD	PBSS3515E	PBSS4032SP	PBSS4160PANP
PBSS302PX	PBSS3515M	PBSS4032SPN	PBSS4160QA
PBSS302PZ	PBSS3515MB	PBSS4041NT	PBSS4160T
PBSS303ND	PBSS3515VS	PBSS4041NX	PBSS4160U
PBSS303NX	PBSS3540E	PBSS4041NZ	PBSS4160V
PBSS303NZ	PBSS3540M	PBSS4041PT	PBSS4220PANS
PBSS303PD	PBSS3540MB	PBSS4041PX	PBSS4220V
PBSS303PX	PBSS4021NT	PBSS4041PZ	PBSS4230PAN
PBSS303PZ	PBSS4021NX	PBSS4041SN	PBSS4230PANP
PBSS304ND	PBSS4021NZ	PBSS4041SP	PBSS4230QA
PBSS304NX	PBSS4021PT	PBSS4041SPN	PBSS4230T
PBSS304NZ	PBSS4021PX	PBSS4112PAN	PBSS4240DPN
PBSS304PD	PBSS4021PZ	PBSS4112PANP	PBSS4240T
PBSS304PX	PBSS4021SN	PBSS4120T	PBSS4240V
PBSS304PZ	PBSS4021SP	PBSS4130PAN	PBSS4240X
PBSS305ND	PBSS4021SPN	PBSS4130PANP	PBSS4240Y
PBSS305NX	PBSS4032ND	PBSS4130QA	PBSS4250X
PBSS305NZ	PBSS4032NT	PBSS4130T	PBSS4260PAN
PBSS305PD	PBSS4032NX	PBSS4140DPN	PBSS4260PANP
PBSS305PX	PBSS4032NZ	PBSS4140T	PBSS4260PANS
PBSS305PZ	PBSS4032PD	PBSS4140U	PBSS4260QA
PBSS306NX	PBSS4032PT	PBSS4140V	PBSS4320T
PBSS306NZ	PBSS4032PX	PBSS4160DPN	PBSS4320X

Multisim 14.1 Education Components

PBSS4330PA	PBSS5130T	PBSS5260QA	PBSS8110T
PBSS4330PAS	PBSS5140T	PBSS5320D	PBSS8110X
PBSS4330X	PBSS5140U	PBSS5320T	PBSS8110Y
PBSS4350D	PBSS5140V	PBSS5320X	PBSS8110Z
PBSS4350SPN	PBSS5160DS	PBSS5330PA	PBSS8510PA
PBSS4350SS	PBSS5160PAP	PBSS5330PAS	PBSS9110D
PBSS4350T	PBSS5160QA	PBSS5330X	PBSS9110T
PBSS4350X	PBSS5160T	PBSS5350D	PBSS9110X
PBSS4350Z	PBSS5160U	PBSS5350SS	PBSS9110Y
PBSS4360Z	PBSS5160V	PBSS5350T	PBSS9110Z
PBSS4420D	PBSS5220PAPS	PBSS5350X	PBSS9410PA
PBSS4440D	PBSS5220T	PBSS5350Z	PCP1208-TD-H
PBSS4480X	PBSS5220V	PBSS5360Z	PCP1302-TD-H
PBSS4520X	PBSS5230PAP	PBSS5420D	PD15-22B/TR8
PBSS4540X	PBSS5230QA	PBSS5440D	PD15-22C/TR8
PBSS4540Z	PBSS5230T	PBSS5480X	PD70-01B/TR7
PBSS4560PA	PBSS5240T	PBSS5520X	PD93-21C/TR8
PBSS4580PA	PBSS5240V	PBSS5540X	PD95-21B/TR10
PBSS4612PA	PBSS5240X	PBSS5540Z	PDB-C134
PBSS4620PA	PBSS5240Y	PBSS5560PA	PDB-C134F
PBSS4630PA	PBSS5250T	PBSS5580PA	PDB-C139
PBSS5112PAP	PBSS5250X	PBSS5612PA	PDB-C142D
PBSS5120T	PBSS5255PAPS	PBSS5620PA	PDB-C152SM
PBSS5130PAP	PBSS5260PAP	PBSS5630PA	PDB-C156
PBSS5130QA	PBSS5260PAPS	PBSS8110D	PDTA113EE

Multisim 14.1 Education Components

PDTA113EM	PDTA115EM	PDTA123YMB	PDTA143TMB
PDTA113EMB	PDTA115EMB	PDTA123YT	PDTA143TT
PDTA113ET	PDTA115ET	PDTA123YU	PDTA143TU
PDTA113EU	PDTA115EU	PDTA124EE	PDTA143XE
PDTA113ZE	PDTA115TE	PDTA124EM	PDTA143XM
PDTA113ZM	PDTA115TM	PDTA124EMB	PDTA143XMB
PDTA113ZMB	PDTA115TMB	PDTA124ET	PDTA143XT
PDTA113ZT	PDTA115TT	PDTA124EU	PDTA143XU
PDTA113ZU	PDTA115TU	PDTA124TE	PDTA143ZE
PDTA114EE	PDTA123EE	PDTA124TM	PDTA143ZM
PDTA114EM	PDTA123EM	PDTA124TMB	PDTA143ZMB
PDTA114EMB	PDTA123EMB	PDTA124TT	PDTA143ZT
PDTA114ET	PDTA123ET	PDTA124TU	PDTA143ZU
PDTA114EU	PDTA123EU	PDTA124XE	PDTA144EE
PDTA114TE	PDTA123JE	PDTA124XM	PDTA144EM
PDTA114TM	PDTA123JM	PDTA124XMB	PDTA144EMB
PDTA114TMB	PDTA123JMB	PDTA124XT	PDTA144ET
PDTA114TT	PDTA123JT	PDTA124XU	PDTA144EU
PDTA114TU	PDTA123JU	PDTA143EE	PDTA144TE
PDTA114YE	PDTA123TM	PDTA143EM	PDTA144TM
PDTA114YM	PDTA123TMB	PDTA143EMB	PDTA144TMB
PDTA114YMB	PDTA123TT	PDTA143ET	PDTA144TT
PDTA114YT	PDTA123TU	PDTA143EU	PDTA144TU
PDTA114YU	PDTA123YE	PDTA143TE	PDTA144VE
PDTA115EE	PDTA123YM	PDTA143TM	PDTA144VM

Multisim 14.1 Education Components

PDTA144VMB	PDTB143ET	PDTC115TE	PDTC124EE
PDTA144VT	PDTB143EU	PDTC115TM	PDTC124EM
PDTA144VU	PDTB143XQA	PDTC115TMB	PDTC124EMB
PDTA144WE	PDTB143XT	PDTC115TT	PDTC124ET
PDTA144WM	PDTB143XU	PDTC115TU	PDTC124EU
PDTA144WMB	PDTC114EE	PDTC123EE	PDTC124TE
PDTA144WT	PDTC114EM	PDTC123EM	PDTC124TM
PDTA144WU	PDTC114EMB	PDTC123EMB	PDTC124TMB
PDTB113EQA	PDTC114ET	PDTC123ET	PDTC124TT
PDTB113ET	PDTC114EU	PDTC123EU	PDTC124TU
PDTB113EU	PDTC114TE	PDTC123JE	PDTC124XE
PDTB113ZQA	PDTC114TM	PDTC123JM	PDTC124XM
PDTB113ZT	PDTC114TMB	PDTC123JMB	PDTC124XMB
PDTB113ZU	PDTC114TT	PDTC123JT	PDTC124XT
PDTB114EQA	PDTC114TU	PDTC123JU	PDTC124XU
PDTB114ET	PDTC114YE	PDTC123TE	PDTC143EE
PDTB114EU	PDTC114YM	PDTC123TM	PDTC143EM
PDTB123EQA	PDTC114YMB	PDTC123TMB	PDTC143EMB
PDTB123ET	PDTC114YT	PDTC123TT	PDTC143ET
PDTB123EU	PDTC114YU	PDTC123TU	PDTC143EU
PDTB123TT	PDTC115EE	PDTC123YE	PDTC143TE
PDTB123YQA	PDTC115EM	PDTC123YM	PDTC143TM
PDTB123YT	PDTC115EMB	PDTC123YMB	PDTC143TMB
PDTB123YU	PDTC115ET	PDTC123YT	PDTC143TT
PDTB143EQA	PDTC115EU	PDTC123YU	PDTC143TU

Multisim 14.1 Education Components

PDTC143XE	PDTC144WE	PDTD143XT	PEMB1
PDTC143XM	PDTC144WM	PDTD143XU	PEMB10
PDTC143XMB	PDTC144WMB	PDZ10B	PEMB11
PDTC143XT	PDTC144WT	PDZ11B	PEMB13
PDTC143XU	PDTC144WU	PDZ12B	PEMB14
PDTC143ZE	PDTD113EQA	PDZ13B	PEMB15
PDTC143ZM	PDTD113ET	PDZ15B	PEMB16
PDTC143ZMB	PDTD113EU	PDZ16B	PEMB17
PDTC143ZT	PDTD113ZQA	PDZ18B	PEMB18
PDTC143ZU	PDTD113ZT	PDZ2.7B	PEMB19
PDTC144EE	PDTD113ZU	PDZ20B	PEMB2
PDTC144EM	PDTD114EQA	PDZ22B	PEMB20
PDTC144EMB	PDTD114ET	PDZ24B	PEMB24
PDTC144ET	PDTD114EU	PDZ3.0B	PEMB3
PDTC144EU	PDTD123EQA	PDZ3.3B	PEMB30
PDTC144TE	PDTD123ET	PDZ3.6B	PEMB4
PDTC144TM	PDTD123EU	PDZ3.9B	PEMB9
PDTC144TMB	PDTD123TT	PDZ4.3B	PEMD10
PDTC144TT	PDTD123YQA	PDZ4.7B	PEMD12
PDTC144TU	PDTD123YT	PDZ5.1B	PEMD13
PDTC144VE	PDTD123YU	PDZ5.6B	PEMD14
PDTC144VM	PDTD143EQA	PDZ6.2B	PEMD15
PDTC144VMB	PDTD143ET	PDZ6.8B	PEMD16
PDTC144VT	PDTD143EU	PDZ7.5B	PEMD17
PDTC144VU	PDTD143XQA	PDZ9.1B	PEMD18

Multisim 14.1 Education Components

PEMD19	PEMH4	PESD15VS1ULD	PESD36VS2UT
PEMD2	PEMH7	PESD15VS2UAT	PESD3V3L1BA
PEMD20	PEMH9	PESD15VS2UQ	PESD3V3L1UA
PEMD24	PEMT1	PESD15VS2UT	PESD3V3L1UB
PEMD3	PEMX1	PESD15VS4UD	PESD3V3L1UL
PEMD30	PEMZ1	PESD15VS5UD	PESD3V3L2BT
PEMD4	PEMZ7	PESD15VU1UT	PESD3V3L2UM
PEMD48	PESD12VL1BA	PESD16VX1UL	PESD3V3L4UF
PEMD6	PESD12VL2BT	PESD1CAN	PESD3V3L4UG
PEMD9	PESD12VS1UA	PESD1FLEX	PESD3V3L4UW
PEMF21	PESD12VS1UB	PESD1LIN	PESD3V3L5UF
PEMH1	PESD12VS1UJ	PESD24VL1BA	PESD3V3L5UK
PEMH10	PESD12VS1UL	PESD24VL2BT	PESD3V3L5UV
PEMH11	PESD12VS1ULD	PESD24VS1UA	PESD3V3L5UY
PEMH13	PESD12VS2UAT	PESD24VS1UB	PESD3V3S1UB
PEMH14	PESD12VS2UQ	PESD24VS1UL	PESD3V3S1UL
PEMH15	PESD12VS2UT	PESD24VS1ULD	PESD3V3S2UAT
PEMH16	PESD12VS4UD	PESD24VS2UAT	PESD3V3S2UQ
PEMH17	PESD12VS5UD	PESD24VS2UQ	PESD3V3S2UT
PEMH18	PESD12VU1UT	PESD24VS2UT	PESD3V3S4UD
PEMH19	PESD12VV1BL	PESD24VS4UD	PESD3V3S4UF
PEMH2	PESD15VL1BA	PESD24VS5UD	PESD3V3S5UD
PEMH20	PESD15VL2BT	PESD24VU1UT	PESD3V3U1UT
PEMH24	PESD15VS1UB	PESD2CAN	PESD3V3V4UF
PEMH30	PESD15VS1UL	PESD36VS1UL	PESD3V3V4UG

Multisim 14.1 Education Components

PESD3V3V4UK	PESD5V0S1BL	PESD5V0V1BLD	PHASE_ANGLE_CONTROLLER_6PULSE
PESD3V3V4UW	PESD5V0S1BLD	PESD5V0V4UF	PHILIPS-MIPS-HDR
PESD5V0F1BL	PESD5V0S1UA	PESD5V0V4UG	PHN110
PESD5V0F1BLD	PESD5V0S1UB	PESD5V0V4UK	PhonePlug
PESD5V0F5UF	PESD5V0S1UJ	PESD5V0V4UW	PhonePlug2
PESD5V0F5UV	PESD5V0S1UL	PESD5V0X1BCAL	PHOTO_DIODE_RATED
PESD5V0L1BA	PESD5V0S1ULD	PESD5V0X1BCL	PHOTO_TRANSISTOR_R_RATED
PESD5V0L1UA	PESD5V0S2BT	PESD5V0X1BL	PHOTODIODE
PESD5V0L1UB	PESD5V0S2UAT	PESD5V0X1BQ	PHOTOTRANSISTOR
PESD5V0L1UL	PESD5V0S2UQ	PESD5V0X1BT	
PESD5V0L1ULD	PESD5V0S4UD	PESD5V0X1UAB	
PESD5V0L2BT	PESD5V0S4UF	PESD5V0X1UALD	PHP125
PESD5V0L2UM	PESD5V0S5UD	PESD5V0X1UB	PHP225
PESD5V0L4UF	PESD5V0U1BA	PESD5V0X1ULD	PHPT60406NY
PESD5V0L4UG	PESD5V0U1BB	PESD5V2S2UT	PHPT60406PY
PESD5V0L4UW	PESD5V0U1BL	PESD9V0V4UK	PHPT60410NY
PESD5V0L5UK	PESD5V0U1BLD	PESD9X5.0L	PHPT60410PY
PESD5V0L5UV	PESD5V0U1UA	PESD9X7.0L	PHPT60415NY
PESD5V0L5UY	PESD5V0U1UB	PG_13	PHPT60415PY
PESD5V0L6UAS	PESD5V0U1UL	PG_9_O_E	PHPT60603NY
PESD5V0L6US	PESD5V0U1UT	PGA281AIPW	PHPT60603PY
PESD5V0L7BAS	PESD5V0U2BT	PHASE_ANGLE_CONTROLLER	PHPT60606NY
PESD5V0L7BS	PESD5V0V1BA		PHPT60606PY
PESD5V0S1BA	PESD5V0V1BB	PHASE_ANGLE_CONTROLLER_2PULSE	PHPT60610NY
PESD5V0S1BB	PESD5V0V1BL		PHPT60610PY

Multisim 14.1 Education Components

PHPT61002NYC	PIMT1	PMBD914	PMBFJ310
PHPT61002PYC	PIMZ2	PMBF170	PMBS3904
PHPT61003NY	PJ-002B-SMT	PMBF4391	PMBS3906
PHPT61003PY	PJ-007	PMBF4392	PMBT2222
PHPT61006NY	PJ1-023	PMBF4393	PMBT2222A
PHPT61006PY	PJ-102A	PMBF4416	PMBT2222AYS
PHPT61010NY	PLD-JTAG-HDR	PMBF4416A	PMBT2369
PHPT61010PY	PLL_VIRTUAL	PMBF5484	PMBT2907
PHT4NQ10LT	PLUS_MINUS_ONE	PMBF5485	PMBT2907A
PHT6N06LT	PLUS_MINUS_ONE_	PMBF5486	PMBT2907AYS
PHT6N06T	BLUE	PMBFJ108	PMBT3904
PHT6NQ10T	PLUS_MINUS_ONE_	PMBFJ109	PMBT3904M
PHT8N06LT	GREEN	PMBFJ110	PMBT3904MB
PI_CONTROLLER	PLUS_MINUS_ONE_	PMBFJ111	PMBT3904VS
PIC16F84	ORANGE	PMBFJ112	PMBT3904YS
PIC16F84A	PLUS_MINUS_ONE_	PMBFJ113	PMBT3906
PID_CONTROLLER	YELLOW	PMBFJ114	PMBT3906M
PIECEWISE_LINEAR	PLVA2656A	PMBFJ175	PMBT3906MB
_CURRENT	PLVA650A	PMBFJ176	PMBT3906VS
PIECEWISE_LINEAR	PLVA662A	PMBFJ177	PMBT3906YS
_VOLTAGE	PMBD353	PMBFJ210	PMBT3946VPN
PIMC31	PMBD354	PMBFJ211	PMBT3946YPN
PIMD2	PMBD6050	PMBFJ212	PMBT4401
PIMD3	PMBD6100	PMBFJ308	PMBT4401YS
PIMH9	PMBD7000	PMBFJ309	PMBT4403
PIMN31	PMBD7100		

Multisim 14.1 Education Components

PMBT4403YS	PMBZ5236B	PMDPB30XN	PMEG060V050EPD
PMBT5550	PMBZ5237B	PMDPB38UNE	PMEG060V100EPD
PMBT5551	PMBZ5238B	PMDPB42UN	PMEG10020AELR
PMBT6428	PMBZ5239B	PMDPB55XP	PMEG100V060ELPD
PMBT6429	PMBZ5240B	PMDPB56XN	PMEG100V080ELPD
PMBTA06	PMBZ5241B	PMDPB56XNEA	PMEG100V100ELPD
PMBTA13	PMBZ5242B	PMDPB58UPE	PMEG1020EA
PMBTA14	PMBZ5243B	PMDPB65UP	PMEG1020EH
PMBTA42	PMBZ5244B	PMDPB70EN	PMEG1020EJ
PMBTA42DS	PMBZ5245B	PMDPB70XP	PMEG1020EV
PMBTA44	PMBZ5246B	PMDPB70XPE	PMEG1030EH
PMBTA45	PMBZ5247B	PMDPB85UPE	PMEG1030EJ
PMBTA56	PMBZ5248B	PMDPB95XNE	PMEG1201AESF
PMBTA64	PMBZ5249B	PMDPB95XNE2	PMEG2002AESF
PMBTA92	PMBZ5250B	PMDT290UNE	PMEG2002ESF
PMBZ5226B	PMBZ5251B	PMDT670UPE	PMEG2005AEA
PMBZ5227B	PMBZ5252B	PMDXB1200UPE	PMEG2005AEL
PMBZ5228B	PMBZ5253B	PMDXB550UNE	PMEG2005AELD
PMBZ5229B	PMBZ5254B	PMDXB600UNE	PMEG2005AESF
PMBZ5230B	PMBZ5255B	PMEG045T150EPD	PMEG2005AEV
PMBZ5231B	PMBZ5256B	PMEG045V050EPD	PMEG2005BELD
PMBZ5232B	PMBZ5257B	PMEG045V100EPD	PMEG2005CT
PMBZ5233B	PMCM440VNE	PMEG045V150EPD	PMEG2005EB
PMBZ5234B	PMCM650VNE	PMEG050T150EPD	PMEG2005EH
PMBZ5235B	PMDPB28UN	PMEG050V150EPD	PMEG2005EJ

Multisim 14.1 Education Components

PMEG2005EL	PMEG2015EPK	PMEG3005ELD	PMEG3020DEP
PMEG2005ELD	PMEG2015EV	PMEG3005ESF	PMEG3020EH
PMEG2005EPK	PMEG2020AEA	PMEG3005ET	PMEG3020EJ
PMEG2005ESF	PMEG2020CPA	PMEG3010AESA	PMEG3020EP
PMEG2005ET	PMEG2020CPAS	PMEG3010AESB	PMEG3020EPA
PMEG2010AEB	PMEG2020EH	PMEG3010BEA	PMEG3020EPAS
PMEG2010AEH	PMEG2020EJ	PMEG3010BEP	PMEG3020ER
PMEG2010AEJ	PMEG2020EPA	PMEG3010BER	PMEG3030BEP
PMEG2010AET	PMEG2020EPAS	PMEG3010BEV	PMEG3030EP
PMEG2010BEA	PMEG2020EPK	PMEG3010CEH	PMEG3050BEP
PMEG2010BELD	PMEG3002AEB	PMEG3010CEJ	PMEG3050EP
PMEG2010BER	PMEG3002AEL	PMEG3010EB	PMEG4002AESF
PMEG2010BEV	PMEG3002AELD	PMEG3010EH	PMEG4002EB
PMEG2010EA	PMEG3002AESF	PMEG3010EJ	PMEG4002EJ
PMEG2010EH	PMEG3002EJ	PMEG3010EP	PMEG4002EL
PMEG2010EJ	PMEG3002ESF	PMEG3010ER	PMEG4002ELD
PMEG2010EPA	PMEG3002TV	PMEG3010ET	PMEG4002ESF
PMEG2010EPAS	PMEG3005AEA	PMEG3015EH	PMEG4005AEA
PMEG2010EPK	PMEG3005AESF	PMEG3015EJ	PMEG4005AESF
PMEG2010ER	PMEG3005AEV	PMEG3015EV	PMEG4005AEV
PMEG2010ET	PMEG3005CT	PMEG3020BEP	PMEG4005CEJ
PMEG2010EV	PMEG3005EB	PMEG3020BER	PMEG4005CT
PMEG2015EA	PMEG3005EH	PMEG3020CEP	PMEG4005EH
PMEG2015EH	PMEG3005EJ	PMEG3020CPA	PMEG4005EJ
PMEG2015EJ	PMEG3005EL	PMEG3020CPAS	PMEG4005EPK

Multisim 14.1 Education Components

PMEG4005ESF	PMEG4030EP	PMEG6020ETR	PMGD370XN
PMEG4005ET	PMEG4030ER	PMEG6030EP	PMGD400UN
PMEG4010AESB	PMEG4030ETP	PMEG6030ETP	PMGD780SN
PMEG4010BEA	PMEG4050EP	PMF170XP	PMGD8000LN
PMEG4010BEV	PMEG4050ETP	PMF250XN	PML260SN
PMEG4010CEH	PMEG45A10EPD	PMF250XNE	PML340SN
PMEG4010CEJ	PMEG45U10EPD	PMF280UN	PMLL4148L
PMEG4010CPA	PMEG6002EB	PMF290XN	PMLL4448
PMEG4010CPAS	PMEG6002EJ	PMF3800SN	PMLL5225B
PMEG4010EH	PMEG6002TV	PMF400UN	PMLL5226B
PMEG4010EJ	PMEG6010AED	PMF63UN	PMLL5227B
PMEG4010EP	PMEG6010CEH	PMF63UNE	PMLL5228B
PMEG4010EPK	PMEG6010CEJ	PMF77XN	PMLL5229B
PMEG4010ER	PMEG6010CPA	PMF780SN	PMLL5230B
PMEG4010ET	PMEG6010CPAS	PMF87EN	PMLL5231B
PMEG4010ETP	PMEG6010ELR	PMFPB6532UP	PMLL5232B
PMEG4010ETR	PMEG6010EP	PMFPB6545UP	PMLL5233B
PMEG4015EPK	PMEG6010ER	PMG370XN	PMLL5234B
PMEG4020EP	PMEG6010ETR	PMG45UN	PMLL5235B
PMEG4020EPA	PMEG6020ELR	PMG85XP	PMLL5236B
PMEG4020EPAS	PMEG6020EP	PMGD130UN	PMLL5237B
PMEG4020EPK	PMEG6020EPA	PMGD175XN	PMLL5238B
PMEG4020ER	PMEG6020EPAS	PMGD175XNE	PMLL5239B
PMEG4020ETP	PMEG6020ER	PMGD280UN	PMLL5240B
PMEG4020ETR	PMEG6020ETP	PMGD290XN	PMLL5241B

Multisim 14.1 Education Components

PMLL5242B	PMMT491A	PMN70XP	PMPB20EN
PMLL5243B	PMMT591A	PMN70XPE	PMPB20UN
PMLL5244B	PMN16XNE	PMN70XPEA	PMPB20XNEA
PMLL5245B	PMN20EN	PMN80XP	PMPB20XPE
PMLL5246B	PMN22XN	PMP4201G	PMPB215ENEA
PMLL5247B	PMN25EN	PMP4201V	PMPB23XNE
PMLL5248B	PMN25UN	PMP4201Y	PMPB27EP
PMLL5249B	PMN27UP	PMP4501G	PMPB29XNE
PMLL5250B	PMN27XPE	PMP4501V	PMPB29XPE
PMLL5251B	PMN27XPEA	PMP4501Y	PMPB33XN
PMLL5252B	PMN28UN	PMP5201G	PMPB33XP
PMLL5253B	PMN30UN	PMP5201V	PMPB43XPE
PMLL5254B	PMN30UNE	PMP5201Y	PMPB47XP
PMLL5255B	PMN30XP	PMP5501G	PMPB85ENEA
PMLL5256B	PMN34UN	PMP5501V	PMPB95ENEA
PMLL5257B	PMN34UP	PMP5501Y	PMR280UN
PMLL5258B	PMN35EN	PMPB10XNE	PMR290UNE
PMLL5259B	PMN40LN	PMPB11EN	PMR290XN
PMLL5260B	PMN40UPE	PMPB12UN	PMR370XN
PMLL5261B	PMN40UPEA	PMPB12UNE	PMR400UN
PMLL5262B	PMN42XPE	PMPB13XNE	PMR670UPE
PMLL5263B	PMN42XPEA	PMPB15XN	PMR780SN
PMLL5264B	PMN48XP	PMPB15XP	PMSS3904
PMLL5265B	PMN50UPE	PMPB16XN	PMSS3906
PMLL5266B	PMN52XP	PMPB19XP	PMST2222

Multisim 14.1 Education Components

PMST2222A	PMV120ENEA	PMV32UP	PMXB360ENEA
PMST2369	PMV130ENEA	PMV33UPE	PMXB40UNE
PMST2907A	PMV160UP	PMV37EN	PMXB43UNE
PMST3904	PMV16UN	PMV37EN2	PMXB56EN
PMST3906	PMV16XN	PMV40UN	PMXB65ENE
PMST4401	PMV170UN	PMV40UN2	PMXB65UPE
PMST4403	PMV185XN	PMV42ENE	PMXB75UPE
PMST5088	PMV20EN	PMV45EN	PMZ1000UN
PMST5089	PMV20XN	PMV45EN2	PMZ1200UPE
PMST5550	PMV20XNE	PMV48XP	PMZ130UNE
PMST5551	PMV20XNEA	PMV50ENEA	PMZ200UNE
PMST6428	PMV213SN	PMV50UPE	PMZ250UN
PMST6429	PMV22EN	PMV50XP	PMZ270XN
PMSTA05	PMV230ENEA	PMV55ENEA	PMZ290UNE
PMSTA06	PMV250EPEA	PMV60EN	PMZ290UNE2
PMSTA42	PMV25ENEA	PMV65ENEA	PMZ320UPE
PMSTA55	PMV27UPE	PMV65UN	PMZ350XN
PMSTA56	PMV27UPEA	PMV65UNE	PMZ390UN
PMSTA92	PMV28UN	PMV65XP	PMZ390UNE
PMT200EN	PMV28UNEA	PMV65XPE	PMZ550UNE
PMT21EN	PMV30UN	PMV65XPEA	PMZ760SN
PMT29EN	PMV30UN2	PMV75UP	PMZB1200UPE
PMT760EN	PMV30XN	PMV90EN	PMZB200UNE
PMV100ENEA	PMV30XPEA	PMXB120EPE	PMZB290UN
PMV117EN	PMV31XN	PMXB350UPE	PMZB290UNE2

Multisim 14.1 Education Components

PMZB300XN	PN3643	PN4916	PQMB11
PMZB320UPE	PN3644	PN4917	PQMD10
PMZB350UPE	PN3645	PN5128	PQMD12
PMZB370UNE	PN3646	PN5129	PQMD13
PMZB380XN	PN3694	PN5133	PQMD16
PMZB390UNE	PN4121	PN5134	PQMD2
PMZB420UN	PN4122	PN5135	PQMD3
PMZB550UNE	PN4141	PN5136	PQMH10
PMZB670UPE	PN4143	PN5137	PQMH11
PMZB790SN	PN4248	PN5138	PQMH13
PN2222	PN4249	PN5139	PQMH2
PN2222A	PN4250	PN5142	PQMH9
PN2369	PN4250A	PN5179	PROBE
PN2369A	PN4258	PN5910	PROBE_BLUE
PN2484	PN4258A	PN930	PROBE_DIG
PN2906	PN4274	PNS40010ER	PROBE_DIG_BLUE
PN2906A	PN4275	POLYNOMIAL_VOLT AGE	PROBE_DIG_GREEN
PN2907	PN4354	POTENTIOMETER	PROBE_DIG_ORAN GE
PN2907A	PN4355	POTENTIOMETER_R ATED	PROBE_DIG_RED
PN3565	PN4356	POTENTIOMETER_V IRTUAL	PROBE_DIG_YELLO W
PN3638	PN4391	Potentiometer1_5K	PROBE_GREEN
PN3638A	PN4392	POWERVCO	PROBE_ORANGE
PN3640	PN4393	POWERVCO2	PROBE_RED
PN3641	PN4416		PROBE_YELLOW
PN3642	PN4416A		

Multisim 14.1 Education Components

PRTR5V0U1T	PSMN022-30PL	PSMN1R3-30YL	PSMN2R6-30YLC
PRTR5V0U2X	PSMN025-100D	PSMN1R5-25YL	PSMN2R6-40YS
PSMN011-60ML	PSMN026-80YS	PSMN1R5-30BLE	PSMN2R6-60PS
PSMN011-60MS	PSMN027-100PS	PSMN1R5-30YL	PSMN2R7-30PL
PSMN011-80YS	PSMN027-100XS	PSMN1R5-30YLC	PSMN2R8-25MLC
PSMN012-100YS	PSMN028-100YS	PSMN1R5-40ES	PSMN2R8-40PS
PSMN012-60YS	PSMN030-60YS	PSMN1R5-40PS	PSMN2R8-80BS
PSMN012-80PS	PSMN034-100PS	PSMN1R6-30PL	PSMN2R9-25YLC
PSMN013-100BS	PSMN038-100YL	PSMN1R6-40YLC	PSMN2R9-30MLC
PSMN013-100ES	PSMN039-100YS	PSMN1R7-30YL	PSMN3R0-30MLC
PSMN013-100PS	PSMN040-100MSE	PSMN1R7-60BS	PSMN3R0-30YL
PSMN013-100XS	PSMN041-80YL	PSMN1R8-30PL	PSMN3R0-60ES
PSMN013-100YSE	PSMN045-80YS	PSMN1R8-40YLC	PSMN3R0-60PS
PSMN013-30MLC	PSMN057-200B	PSMN1R9-40PL	PSMN3R3-40YS
PSMN013-30YLC	PSMN059-150Y	PSMN2R0-30PL	PSMN3R3-60PL
PSMN013-80YS	PSMN069-100YS	PSMN2R0-30YL	PSMN3R3-80BS
PSMN014-40YS	PSMN075-100MSE	PSMN2R0-30YLE	PSMN3R3-80ES
PSMN015-60PS	PSMN0R9-25YLC	PSMN2R0-60ES	PSMN3R3-80PS
PSMN016-100PS	PSMN1R0-30YLC	PSMN2R0-60PS	PSMN3R4-30BLE
PSMN016-100XS	PSMN1R1-25YLC	PSMN2R1-40PL	PSMN3R4-30PL
PSMN017-60YS	PSMN1R1-30PL	PSMN2R2-25YLC	PSMN3R5-30YL
PSMN017-80PS	PSMN1R1-40BS	PSMN2R2-30YLC	PSMN3R5-80ES
PSMN018-80YS	PSMN1R2-25YL	PSMN2R2-40PS	PSMN3R5-80PS
PSMN020-100YS	PSMN1R2-25YLC	PSMN2R5-30YL	PSMN3R8-100BS
PSMN020-30MLC	PSMN1R2-30YLC	PSMN2R5-60PL	PSMN3R9-25MLC

Multisim 14.1 Education Components

PSMN3R9-60PS	PSMN5R6-100PS	PSMN8R3-40YS	PTCSL03T141DT1E
PSMN3R9-60XS	PSMN5R6-100XS	PSMN8R5-100ES	PTCSL03T151DB1E
PSMN4R0-25YLC	PSMN5R8-40YS	PSMN8R5-100PS	PTCSL03T151DT1E
PSMN4R0-30YL	PSMN6R0-25YLB	PSMN8R5-100XS	PTS060301B100RP1 00
PSMN4R0-30YLD	PSMN6R0-30YL	PSMN8R5-60YS	PTS060301B100RP U00
PSMN4R0-40YS	PSMN6R0-30YLB	PSMN8R7-80PS	PTS060302B100RP1 00
PSMN4R1-30YLC	PSMN6R0-30YLD	PSMN9R0-25MLC	PTS060302B100RP U00
PSMN4R2-60PL	PSMN6R1-30YLD	PSMN9R5-100PS	PTS060302B100RP U00
PSMN4R3-100ES	PSMN6R3-120ES	PSMN9R5-100XS	PTS080501B100RP1 00
PSMN4R3-100PS	PSMN6R3-120PS	PSMN9R5-30YLC	PTS080501B100RP U00
PSMN4R3-30PL	PSMN6R5-25YLC	PSMN9R8-30MLC	PTS080501B100RP U00
PSMN4R3-80ES	PSMN6R5-80PS	PSMNR90-30BL	PTS080501B500RP1 00
PSMN4R3-80PS	PSMN7R0-100ES	PTCSL03T081DB1E	PTS080501B500RP U00
PSMN4R4-30MLC	PSMN7R0-100PS	PTCSL03T081DT1E	PTS080502B100RP1 00
PSMN4R4-80PS	PSMN7R0-100XS	PTCSL03T091DB1E	PTS080502B100RP U00
PSMN4R5-40PS	PSMN7R0-30MLC	PTCSL03T091DT1E	PTS080502B100RP1 00
PSMN4R6-100XS	PSMN7R0-30YL	PTCSL03T101DB1E	PTS080502B100RP U00
PSMN4R6-60PS	PSMN7R0-30YLC	PTCSL03T101DT1E	PTS080502B500RP1 00
PSMN4R8-100BSE	PSMN7R0-60YS	PTCSL03T111DB1E	PTS080502B500RP U00
PSMN5R0-100ES	PSMN7R6-100BSE	PTCSL03T111DT1E	PTS080502B500RP U00
PSMN5R0-100PS	PSMN7R6-60PS	PTCSL03T121DB1E	PTS080502B500RP U00
PSMN5R0-100XS	PSMN7R8-120ES	PTCSL03T121DT1E	PTS120601B100RP1 00
PSMN5R0-30YL	PSMN7R8-120PS	PTCSL03T131DB1E	PTS120601B100RP U00
PSMN5R0-80PS	PSMN8R0-40PS	PTCSL03T131DT1E	
PSMN5R5-60YS	PSMN8R2-80YS	PTCSL03T141DB1E	

Multisim 14.1 Education Components

PTS120601B100RP U00	PTVS11VS1UTR	PTVS18VP1UP	PTVS30VP1UTP
PTS120601B1K00P1 00	PTVS12VP1UP	PTVS18VP1UTP	PTVS30VS1UR
PTS120601B1K00P U00	PTVS12VP1UTP	PTVS18VS1UR	PTVS30VS1UTR
PTS120601B1K00P U00	PTVS12VS1UR	PTVS18VS1UTR	PTVS33VP1UP
PTS120601B500RP1 00	PTVS12VS1UTR	PTVS20VP1UP	PTVS33VP1UTP
PTS120601B500RP U00	PTVS13VP1UP	PTVS20VP1UTP	PTVS33VS1UR
PTS120601B500RP U00	PTVS13VP1UTP	PTVS20VS1UR	PTVS33VS1UTR
PTS120601B500RP U00	PTVS13VS1UR	PTVS20VS1UTR	PTVS36VP1UP
PTS120602B100RP1 00	PTVS13VS1UTR	PTVS22VP1UP	PTVS36VP1UTP
PTS120602B100RP U00	PTVS14VP1UP	PTVS22VP1UTP	PTVS36VS1UR
PTS120602B100RP U00	PTVS14VP1UTP	PTVS22VS1UR	PTVS36VS1UTR
PTS120602B1K00P1 00	PTVS14VS1UR	PTVS22VS1UTR	PTVS3V3P1UP
PTS120602B1K00P U00	PTVS14VS1UTR	PTVS24VP1UP	PTVS3V3P1UTP
PTS120602B1K00P U00	PTVS15VP1UP	PTVS24VP1UTP	PTVS3V3S1UR
PTS120602B500RP1 00	PTVS15VP1UTP	PTVS24VS1UR	PTVS3V3S1UTR
PTS120602B500RP U00	PTVS15VS1UR	PTVS24VS1UTR	PTVS40VP1UP
PTS120602B500RP U00	PTVS15VS1UTR	PTVS26VP1UP	PTVS40VP1UTP
PTVS10VP1UP	PTVS16VP1UP	PTVS26VP1UTP	PTVS40VS1UR
PTVS10VP1UTP	PTVS16VP1UTP	PTVS26VS1UR	PTVS40VS1UTR
PTVS10VS1UR	PTVS16VS1UR	PTVS26VS1UTR	PTVS43VP1UP
PTVS10VS1UTR	PTVS16VS1UTR	PTVS28VP1UP	PTVS43VP1UTP
PTVS11VP1UP	PTVS17VP1UP	PTVS28VP1UTP	PTVS43VS1UR
PTVS11VP1UTP	PTVS17VP1UTP	PTVS28VS1UR	PTVS43VS1UTR
PTVS11VS1UR	PTVS17VS1UR	PTVS28VS1UTR	PTVS45VP1UP
	PTVS17VS1UTR	PTVS30VP1UP	PTVS45VP1UTP

Multisim 14.1 Education Components

PTVS45VS1UR	PTVS60VS1UTR	PTVS8V5S1UR	PUMB9
PTVS45VS1UTR	PTVS64VP1UP	PTVS8V5S1UTR	PUMD10
PTVS48VP1UP	PTVS64VP1UTP	PTVS9V0P1UP	PUMD12
PTVS48VP1UTP	PTVS6V0P1UP	PTVS9V0P1UTP	PUMD13
PTVS48VS1UR	PTVS6V0P1UTP	PTVS9V0S1UR	PUMD14
PTVS48VS1UTR	PTVS6V0S1UR	PTVS9V0S1UTR	PUMD15
PTVS51VP1UP	PTVS6V0S1UTR	PULLUP_RATED	PUMD16
PTVS51VP1UTP	PTVS6V5P1UP	PULSE_CURRENT	PUMD17
PTVS51VS1UR	PTVS6V5P1UTP	PULSE_VOLTAGE	PUMD18
PTVS51VS1UTR	PTVS6V5S1UR	PUMB1	PUMD19
PTVS54VP1UP	PTVS6V5S1UTR	PUMB10	PUMD2
PTVS54VP1UTP	PTVS7V0P1UP	PUMB11	PUMD20
PTVS54VS1UR	PTVS7V0P1UTP	PUMB13	PUMD24
PTVS54VS1UTR	PTVS7V0S1UR	PUMB14	PUMD3
PTVS58VP1UP	PTVS7V0S1UTR	PUMB15	PUMD30
PTVS58VP1UTP	PTVS7V5P1UP	PUMB16	PUMD4
PTVS58VS1UR	PTVS7V5P1UTP	PUMB17	PUMD48
PTVS58VS1UTR	PTVS7V5S1UR	PUMB18	PUMD6
PTVS5V0P1UP	PTVS7V5S1UTR	PUMB19	PUMD9
PTVS5V0P1UTP	PTVS8V0P1UP	PUMB2	PUMH1
PTVS5V0S1UR	PTVS8V0P1UTP	PUMB20	PUMH10
PTVS5V0S1UTR	PTVS8V0S1UR	PUMB24	PUMH11
PTVS60VP1UP	PTVS8V0S1UTR	PUMB3	PUMH13
PTVS60VP1UTP	PTVS8V5P1UP	PUMB30	PUMH14
PTVS60VS1UR	PTVS8V5P1UTP	PUMB4	PUMH15

Multisim 14.1 Education Components

PUMH16	PWMCM	PZT43	PZU10DB2
PUMH17	PWMCM2	PZT4401	PZU11B
PUMH18	PWMCMX	PZT4403	PZU11B1
PUMH19	PWMVM	PZT651T1	PZU11B1A
PUMH2	PWMVM2	PZT651T1G	PZU11B2
PUMH20	PXT2222A	PZT751T1	PZU11B2A
PUMH24	PXT2907A	PZT751T1G	PZU11B2L
PUMH30	PXT4401	PZTA14	PZU11B3
PUMH4	PXT4403	PZTA42	PZU11B3A
PUMH7	PXTA14	PZTA42T1	PZU11BA
PUMH9	PXTA42	PZTA42T1G	PZU11BL
PUMT1	PXTA92	PZTA44	PZU11DB2
PUMX1	PZPJ108	PZTA92	PZU12B
PUMX2	PZPJ109	PZTA92T1G	PZU12B1
PUMZ1	PZPJ110	PZTA93	PZU12B1A
PUMZ2	PZT2222	PZU10B	PZU12B2
PUSH_BUTTON_DP ST	PZT2222A	PZU10B1	PZU12B2A
	PZT2222AT1G	PZU10B1A	PZU12B2L
PUSH_CM	PZT2907	PZU10B2	PZU12B3
PUSH_VM	PZT2907A	PZU10B2A	PZU12B3A
	PZT2907AT1	PZU10B2L	PZU12BA
PWM_3PHASE	PZT2907AT1G	PZU10B3	PZU12BL
PWM_COMPLEME NTARY	PZT2907AT3G	PZU10B3A	PZU12DB2
PWM_SINUSOIDAL _3PHASE	PZT3904	PZU10BA	PZU13B
	PZT3906	PZU10BL	PZU13B1

Multisim 14.1 Education Components

PZU13B1A	PZU16B1	PZU2.7B1	PZU22B3
PZU13B2	PZU16B1A	PZU2.7B1A	PZU22B3A
PZU13B2A	PZU16B2	PZU2.7B2	PZU22BA
PZU13B2L	PZU16B2A	PZU2.7B2A	PZU22BL
PZU13B3	PZU16B2L	PZU2.7B2L	PZU22DB2
PZU13B3A	PZU16B3	PZU2.7BA	PZU24B
PZU13BA	PZU16B3A	PZU2.7BL	PZU24B1
PZU13BL	PZU16BA	PZU2.7DB2	PZU24B1A
PZU13DB2	PZU16BL	PZU20B	PZU24B2
PZU14B2	PZU16DB2	PZU20B1	PZU24B2A
PZU14B2A	PZU18B	PZU20B1A	PZU24B2L
PZU14B2L	PZU18B1	PZU20B2	PZU24B3
PZU14DB2	PZU18B1A	PZU20B2A	PZU24B3A
PZU15B	PZU18B2	PZU20B2L	PZU24BA
PZU15B1	PZU18B2A	PZU20B3	PZU24BL
PZU15B1A	PZU18B2L	PZU20B3A	PZU24DB2
PZU15B2	PZU18B3	PZU20BA	PZU27B
PZU15B2A	PZU18B3A	PZU20BL	PZU27BA
PZU15B2L	PZU18BA	PZU20DB2	PZU27BL
PZU15B3	PZU18BL	PZU22B	PZU3.0B
PZU15B3A	PZU18DB2	PZU22B1	PZU3.0B1
PZU15BA	PZU2.4B	PZU22B1A	PZU3.0B1A
PZU15BL	PZU2.4BA	PZU22B2	PZU3.0B2
PZU15DB2	PZU2.4BL	PZU22B2A	PZU3.0B2A
PZU16B	PZU2.7B	PZU22B2L	PZU3.0B2L

Multisim 14.1 Education Components

PZU3.0BA	PZU3.9B2A	PZU4.7B	PZU5.6B2
PZU3.0BL	PZU3.9B2L	PZU4.7B1	PZU5.6B2A
PZU3.0DB2	PZU3.9BA	PZU4.7B1A	PZU5.6B2L
PZU3.3B	PZU3.9BL	PZU4.7B2	PZU5.6B3
PZU3.3B1	PZU3.9DB2	PZU4.7B2A	PZU5.6B3A
PZU3.3B1A	PZU30B	PZU4.7B2L	PZU5.6BA
PZU3.3B2	PZU30BA	PZU4.7B3	PZU5.6BL
PZU3.3B2A	PZU30BL	PZU4.7B3A	PZU5.6DB2
PZU3.3B2L	PZU33B	PZU4.7BA	PZU6.2B
PZU3.3BA	PZU33BA	PZU4.7BL	PZU6.2B1
PZU3.3BL	PZU33BL	PZU4.7DB2	PZU6.2B1A
PZU3.3DB2	PZU36B	PZU5.1B	PZU6.2B2
PZU3.6B	PZU36BA	PZU5.1B1	PZU6.2B2A
PZU3.6B1	PZU36BL	PZU5.1B1A	PZU6.2B2L
PZU3.6B1A	PZU4.3B	PZU5.1B2	PZU6.2B3
PZU3.6B2	PZU4.3B1	PZU5.1B2A	PZU6.2B3A
PZU3.6B2A	PZU4.3B1A	PZU5.1B2L	PZU6.2BA
PZU3.6B2L	PZU4.3B2	PZU5.1B3	PZU6.2BL
PZU3.6BA	PZU4.3B2A	PZU5.1B3A	PZU6.2DB2
PZU3.6BL	PZU4.3B2L	PZU5.1BA	PZU6.8B
PZU3.6DB2	PZU4.3B3	PZU5.1BL	PZU6.8B1
PZU3.9B	PZU4.3B3A	PZU5.1DB2	PZU6.8B1A
PZU3.9B1	PZU4.3BA	PZU5.6B	PZU6.8B2
PZU3.9B1A	PZU4.3BL	PZU5.6B1	PZU6.8B2A
PZU3.9B2	PZU4.3DB2	PZU5.6B1A	PZU6.8B2L

Multisim 14.1 Education Components

PZU6.8B3	PZU8.2BL	RAD_TO_DEG	RD12
PZU6.8B3A	PZU8.2DB2	RB520CS3002L	RD15
PZU6.8BA	PZU9.1B	RB520CS30L	RD15SB
PZU6.8BL	PZU9.1B1	RB520S30	RD2.0S
PZU6.8DB2	PZU9.1B1A	RB521CS30L	RD2.2S
PZU7.5B	PZU9.1B2	RB521S30	RD2.4S
PZU7.5B1	PZU9.1B2A	RB521S30T1G	RD2.7S
PZU7.5B1A	PZU9.1B2L	RB521S30T5G	RD3.0S
PZU7.5B2	PZU9.1B3	RB751CS40	RD4.7
PZU7.5B2A	PZU9.1B3A	RB751S40	RD5.1
PZU7.5B2L	PZU9.1BA	RB751S40T1G	RD5.6
PZU7.5B3	PZU9.1BL	RB751V40	RD6.2
PZU7.5B3A	PZU9.1DB2	RC_CHAIN_CAUER	RD6.8
PZU7.5BA	Quad_And_Gate	RC_CHAIN_FOSTER	RD7.5
PZU7.5BL	QUAD_MUX_2TO1	RC4136D	RD7.5SB
PZU7.5DB2	QUAD_REG	RC4136N	RD8.2
PZU8.2B	R145-32.768kHz	RC4558D	RD9.2
PZU8.2B1	R26-32.768kHz	RC4558P	REF01AJ
PZU8.2B1A	R38-32.768kHz	RC4558Y	REF01AJ/883C
PZU8.2B2	R710XPT	RC4559D	REF01CJ
PZU8.2B2A	R711XPT	RC4559P	REF01CP
PZU8.2B2L	R712XPT	RCJ-011-SMT	REF01CPZ
PZU8.2B3	R714XPT	RCJ-32234	REF01CS
PZU8.2B3A	RAD_PER_SEC_TO_ RPM	RD10	REF01EZ
PZU8.2BA		RD11	REF01HPZ

Multisim 14.1 Education Components

REF01HS	REF193GSZ	REF3230AIDBVR	REF5020ID
REF01HZ	REF194ES	REF3233AIDBVR	REF5020IDGKR
REF02AJ	REF194GP	REF3240AIDBVR	REF5025AID
REF02AJ/883C	REF194GSZ	REF3312AIDBZR	REF5025AIDGKR
REF02AZ	REF195ES	REF3312AIDCKR	REF5025ID
REF02CP	REF195FS	REF3318AIDBZR	REF5025IDGKR
REF02CS	REF195GP	REF3318AIDCKR	REF5030AID
REF02CZ	REF195GPZ	REF3320AIDBZR	REF5030AIDGKR
REF02EZ	REF195GRU	REF3320AIDCKR	REF5030ID
REF02HPZ	REF195GRUZ	REF3325AIDBZR	REF5030IDGKR
REF02HSZ	REF195GS	REF3325AIDCKR	REF5030IDR
REF02HZ	REF196GRU	REF3330AIDBZR	REF5040AID
REF02RC	REF196GRU-REEL7	REF3330AIDCKR	REF5040AIDGKR
REF02RC/883C	REF196GS	REF3333AIDBZR	REF5040AIDR
REF191ES	REF196GSZ	REF3333AIDCKR	REF5040ID
REF191GP	REF198ES	REF43FZ	REF5040IDGKR
REF191GS	REF198FSZ	REF43GP	REF5040IDR
REF192ES	REF198GP	REF43GPZ	REF5045AID
REF192FS	REF198GRU	REF43GS	REF5045AIDGKR
REF192GP	REF198GRUZ	REF5010AID	REF5045AIDR
REF192GPZ	REF198GS	REF5010AIDGKR	REF5045ID
REF192GRU	REF3120AIDBZR	REF5010ID	REF5045IDGKR
REF192GRUZ	REF3212AIDBVR	REF5010IDGKR	REF5045IDR
REF192GS	REF3220AIDBVR	REF5020AID	REF5050AID
REF193GS	REF3225AIDBVR	REF5020AIDGKR	REF5050AIDGKR

Multisim 14.1 Education Components

REF5050AIDR	Resistor3_680	RGP10B	RGP25M
REF5050ID	RESOLVER	RGP10D	RGP30A
REF5050IDGKR	REVERSE_1A	RGP10G	RGP30B
REF5050IDR	REVERSE_2A	RGP10J	RGP30D
REFVAR	REVERSE_3A	RGP10K	RGP30G
REG_FILE_2Px4	REVERSE_4A	RGP10M	RGP30J
REG_FILE_4x4	RGF1A	RGP10M-E3/54	RGP30K
RELAY_COIL	RGF1B	RGP15A	RGP30M
RELAY_COIL_NEGA TED	RGF1D	RGP15B	R-HI-008068-2
RELAY_COIL_PULSE	RGF1G	RGP15D	RIBBON_10H
RELAY_CONTACT_N C	RGF1J	RGP15G	RIBBON_10H_LATC H
RELAY_CONTACT_N O	RGF1K	RGP15J	RIBBON_10H_MNT
RELAY_NC	RGF1M	RGP15K	RIBBON_10V
RELAY_NO	RGL34A	RGP15M	RIBBON_10V_LATC H
RELAY_NONC	RGL34B	RGP20A	RIBBON_10V_MNT
RELAY1A_VIRTUAL	RGL34D	RGP20B	RIBBON_14H
RELAY1B_VIRTUAL	RGL34G	RGP20D	RIBBON_14H_LATC H
RELAY1C_VIRTUAL	RGL34J	RGP20G	RIBBON_14H_MNT
RESET_COIL	RGP02-12E	RGP20J	RIBBON_14V
RESISTOR_RATED	RGP02-14E	RGP25A	RIBBON_14V_LATC H
RESISTOR_VIRTUAL	RGP02-16E	RGP25B	RIBBON_14V_MNT
Resistor1_1.0k	RGP02-18E	RGP25D	RIBBON_16H
Resistor2_4.7k	RGP02-20E	RGP25G	
	RGP02-20E-E3/54	RGP25J	
	RGP10A	RGP25K	

Multisim 14.1 Education Components

RIBBON_16H_LATC H	RIBBON_26V_LATC H	RIBBON_50H_LATC H	S1227-16BQ S1227-16BR
RIBBON_16H_MNT	RIBBON_26V_MNT	RIBBON_50H_MNT	S1227-33BQ S1227-33BR
RIBBON_16V	RIBBON_30H	RIBBON_50V	S1227-66BQ S1227-66BR
RIBBON_16V_LATC H	RIBBON_30H_LATC H	RIBBON_50V_LATC H	S1227-66BR
RIBBON_16V_MNT	RIBBON_30H_MNT	RIBBON_50V_MNT	S1B-E3/61T
RIBBON_20H	RIBBON_30V	RM4136FK	S1D-E3/61T
RIBBON_20H_LATC H	RIBBON_30V_LATC H	RM4136J	S1G-E3/61T
RIBBON_20H_MNT	RIBBON_30V_MNT	RM4136W	S1J-E3/61T
RIBBON_20V	RIBBON_34H	RM4558JG	S1PG-E3/84A
RIBBON_20V_LATC H	RIBBON_34H_LATC H	RMB4S-E3/45	S2800A
RIBBON_20V_MNT	RIBBON_34H_MNT	RPM_TO_RAD_PER _SEC	S2800B
RIBBON_24H	RIBBON_34V	RS1G-E3/5AT	S2800D
RIBBON_24H_LATC H	RIBBON_34V_LATC H	RS1K-E3/61T	S2800M
RIBBON_24H_MNT	RIBBON_34V_MNT	RS2D-E3/52T	S2G-E3/52T
RIBBON_24V	RIBBON_40H	RS2J-E3/52T	S2SA1774G
RIBBON_24V_LATC H	RIBBON_40H_LATC H	RS3D-E3/57T	S2SC4617G
RIBBON_24V_MNT	RIBBON_40H_MNT	RTD	S3D-E3/57T
RIBBON_26H	RIBBON_40V	RV4136D	S3M-E3/57T
RIBBON_26H_LATC H	RIBBON_40V_LATC H	RV4136N	S4PD-M3/86A
RIBBON_26H_MNT	RIBBON_40V_MNT	RV4558D	S5227B
RIBBON_26V	RIBBON_50H	RV4558P	S5227G
		S1227-1010BQ	S5227J
		S1227-1010BR	S5227N

Multisim 14.1 Education Components

SA15AG	SAF-XC866L-1FRA AB	SAF-XC888CM-6FFA 5V AC	SAK-XC2285M- 104F80L AA
SA15ARLG			
SA2M-E3/5AT	SAF-XC866L-1FRA AB	SAF-XC888LM-6FFA 5V AC	SAK-XC2285M- 104F80L AA
SA5.0A-E3/54	SAF-XC886-6FFA 5V AC	SAF-XC888LM-6FFA 5V AC	SAK-XC2285M- 56F80L AA
SA5.0CA-E3/54			
SA6.0A-E3/54	SAF-XC886-6FFA 5V AC	SAK-C167CR-LM HA+	SAK-XC2285M- 56F80L AA
SA6.0CA-E3/54			
SA9.0CA-E3/54	SAF-XC886CLM- 6FFA 5V AC	SAK-C167CR-LM HA+	SAK-XC2285M- 72F80L AA
SAB-C167CR-LM HA+	SAF-XC886CLM- 6FFA 5V AC	SAK-C167SR-LM HA+	SAK-XC2285M- 72F80L AA
SAB-C167CR-LM HA+	SAF-XC886CM-6FFA 5V AC	SAK-C167SR-LM HA+	SAK-XC2286-56F66L AC
SAB-C167SR-LM HA+	SAF-XC886CM-6FFA 5V AC	SAK-XC2264-56F66L AC	SAK-XC2286-56F66L AC
SAB-C167SR-LM HA+	SAF-XC886LM-6FFA 5V AC	SAK-XC2264-56F66L AC	SAK-XC2286-56F80L AC
SAC5.0-E3/54	SAF-XC886LM-6FFA 5V AC	SAK-XC2264-56F80L AC	SAK-XC2286-56F80L AC
SAF-C167CR-LM HA+	SAF-XC888-6FFA 5V AC	SAK-XC2264-56F80L AC	SAK-XC2287-56F66L AC
SAF-C167CR-LM HA+	SAF-XC888-6FFA 5V AC	SAK-XC2267-56F66L AC	SAK-XC2287-56F66L AC
SAF-XC164TM- 4F40F AA	SAF-XC888CLM- 6FFA 5V AC	SAK-XC2267-56F66L AC	SAK-XC2287-56F80L AC
SAF-XC164TM- 4F40F AA	SAF-XC888CLM- 6FFA 5V AC	SAK-XC2267-56F80L AC	SAK-XC2287-56F80L AC
SAF-XC866-1FRA AB			
SAF-XC866-1FRA AB	SAF-XC888CM-6FFA 5V AC	SAK-XC2267-56F80L AC	SAK-XC2287-96F66L AC

Multisim 14.1 Education Components

SAK-XC2287-96F66L AC	SAK-XC866L-1FRA AB	SAK-XC888LM-6FFA 5V AC	SB330 SB340
SAK-XC2287-96F80L AC	SAK-XC886-6FFA 5V AC	SAK-XC888LM-6FFA 5V AC	SB350 SB360
SAK-XC2287-96F80L AC	SAK-XC886-6FFA 5V AC	SAMPLE_BEND SAMPLE_GENERIC	SB3H100-E3/54
SAK-XC2287M- 104F80L AA	SAK-XC886CLM- 6FFA 5V AC	SAMPLE_LOSSY	SB520
SAK-XC2287M- 104F80L AA	SAK-XC886CLM- 6FFA 5V AC	SAMPLE_MICROSTR IP	SB530 SB540
SAK-XC2287M- 56F80L AA	SAK-XC886CM-6FFA 5V AC	SAMPLE_OPENEND SAMPLE_RFCAP	SB540-E3/54 SB550
SAK-XC2287M- 56F80L AA	SAK-XC886CM-6FFA 5V AC	SAMPLE_RFCOIL	SB560
SAK-XC2287M- 72F80L AA	SAK-XC886LM-6FFA 5V AC	SAMPLE_WAVEGUI DE	SB560-E3/54
SAK-XC2287M- 72F80L AA	SAK-XC886LM-6FFA 5V AC	SB SB01-15C-TB-E	SBAS16DXV6T1G SBAS20LT1G
SAK-XC2766X- 96F66L AC	SAK-XC888-6FFA 5V AC	SB040-E3/54 SB05-03Q-TL-E	SBAT54CLT1G SBAV70LT1G
SAK-XC2766X- 96F66L AC	SAK-XC888-6FFA 5V AC	SB1003M3-TL-E	SBAV70LT3G SBAV99LT1G
SAK-XC2786X- 96F66L AC	SAK-XC888CLM- 6FFA 5V AC	SB140A-E3/54 SB160-E3/54	SBAV99LT3G
SAK-XC2786X- 96F66L AC	SAK-XC888CLM- 6FFA 5V AC	SB2H100-E3/54 SB2H90-E3/23	SBAW56LT1G SBAW56LT3G
SAK-XC866-1FRA AB	SAK-XC888CM-6FFA 5V AC	SB3003CH-TL-E	SBAW56TT1G
SAK-XC866-1FRA AB	SAK-XC888CM-6FFA 5V AC	SB3003CH-TL-W	SBC807-16LT1G
SAK-XC866L-1FRA AB		SB320	SBC807-16LT3G SBC807-25LT1G

Multisim 14.1 Education Components

SBC807-25LT3G	SBE002-TL-E	SBRD8360RLG	SD12CT1G
SBC807-40LT1G	SBR640CTT4G	SBRD8360T4G	SD12T1G
SBC807-40LT3G	SBR660CTT4G	SBRD8835LG	SD241
SBC817-25LT1G	SBR80520LT1G	SBRD8835LT4G	SD41
SBC817-25LT3G	SBR80520LT3G	SBRS81100T3G	SDTA114YET1G
SBC846ALT1G	SBR835LT4G	SBRS8120T3G	SDTC114EET1G
SBC846BDW1T1G	SBRA8160T3G	SBRS8130LT3G	SDTC114YET1G
SBC846BLT1G	SBRB1045G	SBRS8140T3G	SDTC124EET1G
SBC846BLT3G	SBRB1045T4G	SBRS8190T3G	SE10PJ-M3/84A
SBC846BPDW1T1G	SBRB1545CTG	SBRS8320T3G	SE5534AFK
SBC846BPDW1T2G	SBRB1545CTT4G	SBRS8340T3G	SE5534AJG
SBC847BDW1T1G	SBRB20200CTT4G	SBS811-TL-E	SE5534FK
SBC847BDW1T3G	SBRB2545CTG	SCH1330-TL-H	SE5534JG
SBC856ALT1G	SBRB2545CTT4G	SCH1330-TL-W	SEAM-40-03.0-S-06-2-A-K-TR
SBC856BDW1T1G	SBRD81035CTLT4G	SCH1433-TL-H	SEAM-40-07.0-S-06-2-A-K-TR
SBC856BDW1T3G	SBRD81045T4G	SCH1433-TL-W	SEAM-40-07.0-S-06-2-A-K-TR
SBC856BWT1G	SBRD8320G	SCH1435-TL-H	SEMICONDUCTOR_
SBC857BDW1T1G	SBRD8320T4G	SCH1435-TL-W	CAPACITOR_VIRTU
SBCP56-10T1G	SBRD8330G	SCH1439-TL-H	AL
SBCP56-16T1G	SBRD8330T4G	SCH1439-TL-W	SEMICONDUCTOR_
SBCP56-16T3G	SBRD8340G	SCH2202-TL-E	RESISTOR_VIRTUAL
SBCP56T1G	SBRD8340T4G	SCHMITT_TRIGGER	SEPICCM
SBCP56T3G	SBRD8350G	SCR	SEPICVM
SBCP68T1G	SBRD8350T4G	SCY99074DR2G	SET_COIL
SBE001-TL-E	SBRD8360G	SD05T1G	SEVEN_SEG_COM_
			A

Multisim 14.1 Education Components

SEVEN_SEG_COM_A_BLUE	SEVEN_SEG_DECIMAL_COM_K_BLUE	SEVEN_SEG_TWO-DIGIT_COM_K_ORANGE	SFH615A-3X001
SEVEN_SEG_COM_A_GREEN	SEVEN_SEG_DECIMAL_COM_K_GREEN	SEVEN_SEG_TWO-DIGIT_COM_K_YELLOW	SFH615A-3X006
SEVEN_SEG_COM_A_ORANGE	SEVEN_SEG_DECIMAL_COM_K_ORANGE	SFH 203 FA	SFH615A-3X007T
SEVEN_SEG_COM_A_YELLOW	SEVEN_SEG_DECIMAL_COM_K_YELLOW	SFH 205 F	SFH615A-3X009T
SEVEN_SEG_COM_K	SEVEN_SEG_TWO-DIGIT_COM_A	SFH 206 K	SFH615A-3X016
SEVEN_SEG_COM_K_BLUE	SEVEN_SEG_TWO-DIGIT_COM_A_BLUE	SFH 213	SFH615A-3X017
SEVEN_SEG_COM_K_GREEN	SEVEN_SEG_TWO-DIGIT_COM_A_GREEN	SFH 229 FA	SFH617A-3
SEVEN_SEG_COM_K_ORANGE	SEVEN_SEG_TWO-DIGIT_COM_A_ORANGE	SFH 2400 FA	SFH617A-3X001
SEVEN_SEG_COM_K_YELLOW	SEVEN_SEG_TWO-DIGIT_COM_A_YELLOW	SFH 2500 FA-Z	SFH617A-3X006
SEVEN_SEG_DECIMAL_COM_A	SEVEN_SEG_TWO-DIGIT_COM_A_YELLOW	SFH 2505 FA-Z	SFH617A-3X007T
SEVEN_SEG_DECIMAL_COM_A_BLUE	SEVEN_SEG_TWO-DIGIT_COM_K	SFH6136	SFH617A-3X016
SEVEN_SEG_DECIMAL_COM_A_GREEN	SEVEN_SEG_TWO-DIGIT_COM_K_BLUE	SFH6136-X001	SFH617A-3X017T
SEVEN_SEG_DECIMAL_COM_A_ORANGE	SEVEN_SEG_TWO-DIGIT_COM_K_GREEN	SFH6136-X006	SFH6316T
SEVEN_SEG_DECIMAL_COM_A_YELLOW	SEVEN_SEG_TWO-DIGIT_COM_K_ORANGE	SFH6136-X007	SFH6343T
SEVEN_SEG_DECIMAL_COM_K	SEVEN_SEG_TWO-DIGIT_COM_K_YELLOW	SFH6136-X009T	SFH6700
		SFH6136-X016	SFH6700-X009
		SFH6136-X017T	SFH6701
		SFH6136-X018	SFH6701-X007
		SFH6136-X019T	SFH6701-X009
		SFH6156-3	SFH6702
		SFH6156-3T	SFH6702-X006
		SFH615A-3	SFH6702-X007
			SFH6702-X009T
			SFH6705
			SFH6705-X006

Multisim 14.1 Education Components

SFH6705-X007	SFT1446-H	Si1467DH-T1-GE3	Si2343CDS-T1-GE3
SFH6711	SFT1446-TL-H	Si1469DH-T1-GE3	Si2366DS-T1-GE3
SFH6711-X007	SGL41-40-E3/96	Si1471DH-T1-GE3	Si2367DS-T1-GE3
SFH6712	SHIFT_4BIDI	Si2300DS-T1-GE3	Si2371EDS-T1-GE3
SFH6712-X007	SHIFT_4PIPO	Si2301CDS-T1-GE3	Si2372DS-T1-GE3
SFH6719	SHIFT_8PIN	Si2302DS	Si2374DS-T1-GE3
SFH6720T	SHIFT_8POUT	Si2303CDS-T1-GE3	Si2392ADS-T1-GE3
SFH6721T	Shift_Register_74LS 165N	Si2304DDS-T1-GE3	Si2399DS-T1-GE3
SFH6755T	Si1002R-T1-GE3	Si2304DS	Si3127DV-T1-GE3
SFH6756T	Si1012CR-T1-GE3	Si2305CDS-T1-GE3	Si3429EDV-T1-GE3
SFH6757T	Si1016CX-T1-GE3	Si2307CDS-T1-GE3	Si3443DDV-T1-GE3
SFH690CT	Si1036X-T1-GE3	Si2308BDS-T1-GE3	Si4128DY-T1-GE3
SFH690C-X001T	Si1050X-T1-GE3	Si2309CDS-T1-GE3	Si4143DY-T1-GE3
SFT1341-E	Si1069X-T1-GE3	Si2312CDS-T1-GE3	Si4434DY-T1-GE3
SFT1341-TL-E	Si1070X-T1-GE3	Si2318CDS-T1-GE3	Si4491EDY-T1-GE3
SFT1345-H	Si1071X-T1-GE3	Si2319CDS-T1-GE3	Si4590DY-T1-GE3
SFT1345-TL-H	Si1302DL-T1-GE3	Si2323CDS-T1-GE3	Si5411EDU-T1-GE3
SFT1350-H	Si1317DL-T1-GE3	Si2324DS-T1-GE3	Si5429DU-T1-GE3
SFT1350-TL-H	Si1403CDL-T1-GE3	Si2325DS-T1-GE3	Si5936DU-T1-GE3
SFT1423-E	Si1411DH-T1-GE3	Si2328DS-T1-GE3	Si7121ADN-T1-GE3
SFT1423-TL-E	Si1414DH-T1-GE3	Si2329DS-T1-GE3	Si7148DP-T1-GE3
SFT1440-E	Si1416EDH-T1-GE3	Si2336DS-T1-GE3	Si7149ADP-T1-GE3
SFT1440-H	Si1422DH-T1-GE3	Si2337DS-T1-GE3	Si7370DP-T1-GE3
SFT1440-TL-E	Si1442DH-T1-GE3	Si2338DS-T1-GE3	Si7454DDP-T1-GE3
SFT1440-TL-H		Si2342DS-T1-GE3	Si7456CDP-T1-GE3

Multisim 14.1 Education Components

Si7456DDP-T1-GE3	SiA413ADJ-T1-GE3	SiHB12N60E-GE3	SiHF23N60E-GE3
Si7846DP-T1-GE3	SiA431DJ-T1-GE3	SiHB12N65E-GE3	SiHF28N60EF-GE3
Si7852DP-T1-GE3	SiA437DJ-T1-GE3	SiHB15N50E-GE3	SiHF30N60E-GE3
Si7946ADP-T1-GE3	SiA440DJ-T1-GE3	SiHB15N60E-GE3	SiHF6N65E-GE3
Si8406DB-T2-E1	SiA442DJ-T1-GE3	SiHB15N65E-GE3	SiHF7N60E-GE3
Si8410DB-T2-E1	SiA446DJ-T1-GE3	SiHB20N50E-GE3	SiHG17N60D-GE3
Si8416DB-T2-E1	SiA459EDJ-T1-GE3	SiHB21N60EF-GE3	SiHG21N60EF-GE3
Si8424CDB-T1-E1	SiA461DJ-T1-GE3	SiHB21N65EF-GE3	SiHG21N65EF-GE3
Si8425DB-T1-E1	SiA462DJ-T1-GE3	SiHB22N65E-GE3	SiHG22N65E-GE3
Si8457DB-T1-E1	SiA466EDJ-T1-GE3	SiHB23N60E-GE3	SiHG23N60E-GE3
Si8461DB-T2-E1	SiA906EDJ-T1-GE3	SiHB24N65E-GE3	SiHG24N65E-GE3
Si8466EDB-T2-E1	SiA914ADJ-T1-GE3	SiHB28N60EF-GE3	SiHG25N50E-GE3
Si8469DB-T2-E1	SiA922EDJ-T1-GE3	SiHB30N60E-GE3	SiHG28N60EF-GE3
Si8472DB-T2-E1	SiA931DJ-T1-GE3	SiHB33N60EF-GE3	SiHG28N65EF-GE3
Si8483DB-T2-E1	SiA936EDJ-T1-GE3	SiHB33N60E-GE3	SiHG28N65E-GE3
Si8487DB-T1-E1	SiHA12N50E-E3	SiHB6N65E-GE3	SiHG30N60E-GE3
Si8497DB-T2-E1	SiHA12N60E-E3	SiHD12N50E-GE3	SiHG33N60EF-GE3
Si8499DB-T2-E1	SiHA14N60E-E3	SiHD6N62E-GE3	SiHG33N60E-GE3
Si8800EDB-T2-E1	SiHA15N50E-E3	SiHD6N65E-GE3	SiHG33N65EF-GE3
Si8802DB-T2-E1	SiHA15N60E-E3	SiHD7N60E-GE3	SiHG47N60EF-GE3
Si8810EDB-T2-E1	SiHA20N50E-E3	SiHF12N60E-GE3	SiHG47N65E-GE3
Si8816EDB-T2-E1	SiHA21N60EF-E3	SiHF12N65E-GE3	SiHG64N65E-GE3
Si8824EDB-T2-E1	SiHA22N60E-E3	SiHF15N60E-GE3	SiHG70N60EF-GE3
Si8851EDB-T2-E1	SiHA25N50E-E3	SiHF15N65E-GE3	SiHG73N60E-GE3
SiA406DJ-T1-GE3	SiHB12N50E-GE3	SiHF22N65E-GE3	

Multisim 14.1 Education Components

SiHH11N60EF-T1-GE3	SiHP24N65E-GE3	SiS407ADN-T1-GE3	SL12-E3/5AT
	SiHP25N50E-GE3	SiS413DN-T1-GE3	SL13-E3/61T
SiHH11N60E-T1-GE3	SiHP28N60EF-GE3	SiS429DNT-T1-GE3	SL22-E3/52T
SiHH14N60EF-T1-GE3	SiHP28N65EF-GE3	SiS435DNT-T1-GE3	SL23-E3/52T
	SiHP28N65E-GE3	SiS439DNT-T1-GE3	SL43-E3/57T
SiHH14N60E-T1-GE3	SiHP30N60E-GE3	SiS443DN-T1-GE3	SL44-E3/57T
SiHH14N65E-T1-GE3	SiHP33N60EF-GE3	SiS447DN-T1-GE3	SLOW_1A
	SiHP33N60E-GE3	SiS488DN-T1-GE3	SLOW_2A
SiHH21N60EF-T1-GE3	SiHP6N65E-GE3	SiS626DN-T1-GE3	SLOW_3A
	SiHP7N60E-GE3	SiS822DNT-T1-GE3	SLOW_4A
SiHH21N65EF-T1-GE3	SiHU6N62E-GE3	SiS888DN-T1-GE3	SM05T1G
SiHH24N65EF-T1-GE3	SiHU6N65E-GE3	SiS890DN-T1-GE3	SM12T1G
	SiHU7N60E-GE3	SiS990DN-T1-GE3	SM15T150A-E3/57T
SiHH24N65E-T1-GE3	SiHW33N60E-GE3	SiSA10DN-T1-GE3	SM15T150CA-E3/9AT
	SiJ462DP-T1-GE3	SiSA14DN-T1-GE3	SM15T18A-E3/57T
SiHH26N60EF-T1-GE3	SiJ470DP-T1-GE3	SiSA34DN-T1-GE3	SM15T24A-E3/9AT
SiHP12N50E-GE3	SiJ478DP-T1-GE3	SiSS10DN-T1-GE3	SM15T33A-E3/57T
SiHP12N60E-GE3	SiR472ADP-T1-GE3	SiSS40DN-T1-GE3	SM15T68A-E3/57T
SiHP15N50E-GE3	SiR472DP-T1-GE3	SiUD402ED-T1-GE3	SM15T68CA-E3/57T
SiHP15N60E-GE3	SiR638DP-T1-GE3	SiZ340DT-T1-GE3	SM3G45
SiHP15N65E-GE3	SiR640ADP-T1-GE3	SiZ342DT-T1-GE3	SM3J45
SiHP18N60E-GE3	SiR644DP-T1-GE3	SiZ980DT-T1-GE3	SM5S20AHE3/2D
SiHP20N50E-GE3	SiR696DP-T1-GE3	SiZ998DT-T1-GE3	SM5S22AHE3/2D
SiHP21N60EF-GE3	SiR804DP-T1-GE3	SJ1-3515N	SM5S26AHE3/2D
SiHP21N65EF-GE3	SiR880ADP-T1-GE3	SL05T1G	

Multisim 14.1 Education Components

SM5S33AHE3/2D	SMAJ24A-E3/61	SMBJ45A-E3/52	SMBT5087
SM5S36AHE3/2D	SMAJ24CA-E3/61	SMBJ48A-E3/52	SMBT6428
SM6S33AHE3/2D	SMAJ26A-E3/61	SMBJ48CA-E3/52	SMBT6429
SM6T12A-E3/52	SMAJ28CA-E3/61	SMBJ5.0CA-E3/52	SMBTA05
SM8S12AHE3/2D	SMAJ36A-E3/61	SMBJ58A-E3/52	SMBTA06
SM8S14AHE3/2D	SMAJ40CA-E3/61	SMBJ58CA-E3/52	SMBTA20
SM8S15AHE3/2D	SMAJ530-E3/61	SMBJ6.0A-E3/52	SMBTA42
SM8S16AHE3/2D	SMAJ6.5A-E3/61	SMBJ70A-E3/52	SMBTA43
SM8S17AHE3/2D	SMAJ60A-E3/61	SMBJ8.0A-E3/52	SMBTA55
SM8S18AHE3/2D	SMBJ28CA-E3/52	SMBJ8.0CA-E3/52	SMBTA56
SM8S22AHE3/2D	SMBJ14A-E3/52	SMBJ85A-E3/52	SMBTA56C
SM8S24AHE3/2D	SMBJ15CA-E3/52	SMBT2222A	SMBTA70
SM8S26AHE3/2D	SMBJ170A-E3/52	SMBT2907	SMBTA92
SM8S30AHE3/2D	SMBJ170CA-E3/52	SMBT2907A	SMBTA93
SM8S33AHE3/2D	SMBJ188CA-E3/52	SMBT35200MT1G	SMCJ12A-E3/57T
SM8S36AHE3/2D	SMBJ22A-E3/52	SMBT3903	SMCJ130CA-E3/57T
SM8S43AHE3/2D	SMBJ24CA-E3/52	SMBT3904	SMCJ15A-E3/57T
SMA5J28A-E3/61	SMBJ26CA-E3/52	SMBT3906	SMCJ15CA-E3/57T
SMAJ11A-E3/61	SMBJ28CA-E3/52	SMBT3906S	SMCJ16CA-E3/57T
SMAJ11CA-E3/61	SMBJ30A-E3/52	SMBT3946DW1T1G	SMCJ18A-E3/57T
SMAJ12A-E3/61	SMBJ33A-E3/52	SMBT4124	SMCJ18CA-E3/57T
SMAJ12CA-E3/61	SMBJ33CA-E3/52	SMBT4126	SMCJ26CA-E3/57T
SMAJ150CA-E3/61	SMBJ36A-E3/52	SMBT4401	SMCJ28CA-E3/57T
SMAJ15A-E3/61	SMBJ36CA-E3/52	SMBT4403	SMCJ30CA-E3/57T
SMAJ16A-E3/61	SMBJ3V3-E3/52	SMBT5086	SMCJ33CA-E3/57T

Multisim 14.1 Education Components

SMCJ36CA-E3/57T	SMF58AT1G	SML4754	SMMBT3904TT1G
SMCJ48CA-E3/57T	SMF6.0AT1G	SML4755	SMMBT4401LT1G
SMCJ5.0CA-E3/57T	SMF6.5AT1G	SML4756	SMMBT4403LT1G
SMCJ51CA-E3/57T	SMF7.0AT1G	SML4757	SMMBT5401LT1G
SMCJ58A-E3/57T	SMF7.5AT1G	SML4758	SMMBT5551LT1G
SMCJ6.5A-E3/57T	SMF8.0AT1G	SML4759	SMMBT5551LT3G
SMCJ75A-E3/57T	SML4735	SML4760	SMMBTA06LT1G
SMCJ78A-E3/57T	SML4736	SML4761	SMMBTA06LT3G
SMCJ8.5A-E3/57T	SML4737	SML4762	SMMBTA06WT1G
SMF05CT1G	SML4738	SML4763	SMMBTA14LT1G
SMF05CT2G	SML4739	SMM2348ES-T1-GE3	SMMBTA42LT1G
SMF12AT1G	SML4740	SMMBD2837LT1G	SMMBTA42LT3G
SMF12CT1G	SML4741	SMMBD301LT3G	SMMBTA56LT1G
SMF15CT1G	SML4742	SMMBD7000LT1G	SMMBTA56LT3G
SMF18AT1G	SML4743	SMMBD7000LT3G	SMMBTA92LT1G
SMF22AT1G	SML4744	SMMBD770T1G	SMMBTA92LT3G
SMF24AT1G	SML4745	SMMBD914LT1G	SMMDL914T1G
SMF24CT1G	SML4746	SMMBD914LT3G	SMMJT350T1G
SMF26AT1G	SML4747	SMMBT2222ALT1G	SMMSD301T1G
SMF28AT1G	SML4748	SMMBT2222ALT3G	SMMSD4148T1G
SMF30AT1G	SML4749	SMMBT2369ALT1G	SMMSD4148T3G
SMF33AT1G	SML4750	SMMBT2907ALT1G	SMMUN2111LT1G
SMF36AT1G	SML4751	SMMBT2907ALT3G	SMMUN2111LT3G
SMF48AT1G	SML4752	SMMBT3904LT1G	SMMUN2113LT1G
SMF5.0AT1G	SML4753		SMMUN2114LT1G

Multisim 14.1 Education Components

SMMUN2116LT1G	SMUN5112DW1T1 G	SMUN5230DW1T1 G	SN10502DGN
SMMUN2116LT3G			SN200501036DRE4
SMMUN2134LT1G	SMUN5112T1G	SMUN5232DW1T1 G	SN412008DRE4
SMMUN2211LT1G	SMUN5113DW1T1 G	SMUN5232T1G	SN7002N
SMMUN2211LT3G	SMUN5113T1G	SMUN5233DW1T1 G	SN7002W
SMMUN2213LT1G	SMUN5114DW1T1 G		SN74121N
SMMUN2213LT3G		SMUN5233T1G	SN74123D
SMMUN2214LT1G	SMUN5114T1G	SMUN5235DW1T1 G	SN74123FK
SMMUN2215LT1G	SMUN5115DW1T1 G	SMUN5237DW1T1 G	SN74123N
SMMUN2216LT1G	SMUN5115T1G		SN74130N
SMMUN2216LT3G	SMUN5116DW1T1 G	SMUN5311DW1T2 G	SN74LVC2G66QDC URQ1
SMMUN2233LT1G		SMUN5312DW1T1 G	SNSS30201MR6T1G
SMMUN2234LT1G	SMUN5133T1G		SNSS35200MR6T1G
SMP3003-DL-1E	SMUN5211T1G	SMUN5313DW1T1 G	SNSS40600CF8T1G
SMP3003-TL-1E	SMUN5211T3G		SNUF6401MNT1G
SMS05T1G	SMUN5212T1G	SMUN5314DW1T1 G	SONALERT
SMUN2111T1G	SMUN5213DW1T1 G	SMUN5315DW1T1 G	SPA02N80C3
SMUN2111T3G			SPA03N60C3
SMUN2114T1G	SMUN5213T1G	SMUN5330DW1T1 G	SPA04N50C3
SMUN2211T1G	SMUN5214DW1T1 G	SMUN5335DW1T1 G	SPA04N60C3
SMUN2211T3G	SMUN5214T1G		SPA04N80C3
SMUN2216T1G	SMUN5215T1G	SMUN5335DW1T2 G	SPA06N60C3
SMUN2230T1G	SMUN5216DW1T1 G		SPA06N80C3
SMUN2232T1G		SN10502D	SPA07N60C3
SMUN2240T1G		SN10502DGK	

Multisim 14.1 Education Components

SPA07N60CFD	SPB07N60C3	SPD04N80C3	SPI07N60C3
SPA07N65C3	SPB07N60S5	SPD04P10P G	SPI07N60S5
SPA08N50C3	SPB08P06P G	SPD04P10PL G	SPI08N50C3
SPA08N80C3	SPB100N03S2-03 G	SPD06N60C3	SPI08N80C3
SPA11N60C3	SPB11N60C3	SPD06N80C3	SPI11N60C3
SPA11N60CFD	SPB11N60S5	SPD07N60C3	SPI11N60CFD
SPA11N65C3	SPB12N50C3	SPD07N60S5	SPI11N60S5
SPA11N80C3	SPB16N50C3	SPD08N50C3	SPI12N50C3
SPA12N50C3	SPB17N80C3	SPD08P06P G	SPI15N60C3
SPA15N60C3	SPB18P06P G	SPD09P06PL G	SPI15N60CFD
SPA15N60CFD	SPB20N60C3	SPD15P10P G	SPI15N65C3
SPA15N65C3	SPB20N60S5	SPD15P10PL G	SPI16N50C3
SPA16N50C3	SPB21N50C3	SPD18P06P G	SPI20N60C3
SPA17N80C3	SPB80P06P G	SPD30N03S2L-07 G	SPI20N60CFD
SPA20N60C3	SPD01N60C3	SPD30N03S2L-10 G	SPI21N50C3
SPA20N60CFD	SPD02N50C3	SPD30N03S2L-20 G	SPP02N60C3
SPA20N65C3	SPD02N60C3	SPD30P06P G	SPP02N60S5
SPA21N50C3	SPD02N60S5	SPD50N03S2-07 G	SPP02N80C3
SPB02N60C3	SPD02N80C3	SPD50N03S2L-06 G	SPP03N60C3
SPB02N60S5	SPD03N50C3	SPD50P03L G	SPP03N60S5
SPB03N60C3	SPD03N60C3	SPDT	SPP04N50C3
SPB03N60S5	SPD03N60S5	SPDT_CLOSED	SPP04N60C3
SPB04N50C3	SPD04N50C3	SPDT_OPEN	SPP04N60S5
SPB04N60C3	SPD04N60C3	SPEED_F	SPP04N80C3
SPB04N60S5	SPD04N60S5	SPEED_FR	SPP06N60C3

Multisim 14.1 Education Components

SPP06N80C3	SPP21N50C3	SPW12N50C3	SQ2308CES-T1-GE3
SPP07N60C3	SPP24N60C3	SPW15N60C3	SQ2318AES-T1-GE3
SPP07N60CFD	SPP24N60CFD	SPW15N60CFD	SQ2337ES-T1-GE3
SPP07N60S5	SPP80P06P H	SPW16N50C3	SQ2348ES-T1-GE3
SPP07N65C3	SPST	SPW17N80C3	SQ2361EES-T1-GE3
SPP08N50C3	SPST_CLOSED	SPW20N60C3	SQ2361ES-T1-GE3
SPP08N80C3	SPST_NC_DB	SPW20N60CFD	SQ2389ES-T1-GE3
SPP08P06P H	SPST_NC_SB	SPW20N60S5	SQ3410EV-T1-GE3
SPP11N60C3	SPST_NO_DB	SPW21N50C3	SQ3418EEV-T1-GE3
SPP11N60CFD	SPST_NO_SB	SPW24N60C3	SQ3456BEV-T1-GE3
SPP11N60S5	SPST_OPEN	SPW24N60CFD	SQ3469EV-T1-GE3
SPP11N65C3	SPU01N60C3	SPW32N50C3	SQ4184EY-T1-GE3
SPP11N80C3	SPU02N60C3	SPW35N60C3	SQ4284EY-T1-GE3
SPP12N50C3	SPU02N60S5	SPW35N60CFD	SQ4435EY-T1-GE3
SPP15N60C3	SPU03N60C3	SPW47N60C3	SQ4917EY-T1-GE3
SPP15N60CFD	SPU03N60S5	SPW47N60CFD	SQ7414AEN-T1-GE3
SPP15P10P H	SPU04N60C3	SPW47N65C3	SQ7414AENW-T1-GE3
SPP15P10PL H	SPU04N60S5	SPW52N50C3	SQA410EJ-T1-GE3
SPP16N50C3	SPU07N60C3	SPZT2222AT1G	SQD100N03-3m2L-GE3
SPP17N80C3	SPU07N60S5	SPZT2907AT1G	SQD100N04-3m6-GE3
SPP18P06P H	SPW07N60CFD	SPZT651T1G	SQD100N04-3m6L-GE3
SPP20N60C3	SPW11N60C3	SPZTA42T1G	SQD100N04-3m6L-GE3
SPP20N60CFD	SPW11N60CFD	SQ1421EEH-T1-GE3	SQD45P03-12-GE3
SPP20N60S5	SPW11N60S5	SQ1470AEH-T1-GE3	
SPP20N65C3	SPW11N80C3	SQ1902EL-T1-GE3	

Multisim 14.1 Education Components

SQD50N04-5m6-GE3	SQM200N04-1m7L-GE3	SQV120N10-3m8-GE3	SS1H10-E3/5AT
			SS1P3L-M3/84A
SQD50P08-28-GE3	SQM200N04-1m8-GE3	SR_4BIDI	SS1P4L-M3/84A
SQD90P04-9m4L-GE3	SQM35N30-97-GE3	SR_4P_P_3SO	SS1P4-M3/84A
SQJ443EP-T1-GE3	SQM50020EL-GE3	SR_4P_P_INV	SS1P6L-E3/84A
SQJ459EP-T1-GE3	SQM50P03-07-GE3	SR_4S_P	SS22T3G
SQJ460AEP-T1-GE3	SQM60030E-GE3	SR_8P_2S	SS24-E3/52T
SQJ461EP-T1-GE3	SQM60N20-35-GE3	SR_8P_S	SS24S-E3/61T
SQJ465EP-T1-GE3	SQP100N04-3m6-GE3	SR_8P_S_C	SS24T3
SQJ486EP-T1-GE3	SQP100P06-9m3L-GE3	SR_8PS_S_AS	SS24T3G
SQJ500AEP-T1-GE3	SQP100P06-9m3L-GE3	SR_8PS_S_SL	SS26-E3/52T
SQJ844AEP-T1-GE3	SQP120N10-09-GE3	SR_8S_P	SS26T3
SQJ910AEP-T1-GE3	SQP120N10-3m8-GE3	SR_FF	SS26T3G
SQJ951EP-T1-GE3	SQP25N15-52-GE3	SR_FF_NEGSR	SS2H10-E3/2CT
SQJ980AEP-T1-GE3	SQP50N06-09L-GE3	SR_FF_POSSR	SS2P3L-M3/84A
SQM100P10-19L-GE3	SQP50P03-07-GE3	SR_LATCH	SS2P4-M3/84A
SQM110P06-8m9L-GE3	SQP60N06-15-GE3	SR_LATCH_NEGSR	SS2PH10-M3/84A
SQM120N04-1m7-GE3	SQR40N10-25-GE3	SS0503SH-TL-E	SS32
SQM120N04-1m9-GE3	SQR50N04-3m8-GE3	SS10P3-M3/86A	SS32-E3/57T
SQM120N04-1m9-GE3	SQR97N06-6m3L-GE3	SS10P4-M3/86A	SS33
SQM120N06-3m5L-GE3	SQS482EN-T1-GE3	SS10P6-M3/86A	SS34
SQM120N10-3m8-GE3	SQS840EN-T1-GE3	SS10PH10-M3/86A	SS34-E3/57T
	SQS850EN-T1-GE3	SS14-E3/61T	SS35
		SS16-E3/61T	SS36-E3/57T
		SS16T3G	SS3H9-E3/57T

Multisim 14.1 Education Components

SS3P4HM3/84A	STD5406NT4G	SUM90140E-GE3	SUR83060PTG
SS3P4LHM3/86A	STD5407NT4G	SUP40010EL-GE3	SUR8820G
SS3P6-E3/84A	STEP_CURRENT	SUP40N25-60-E3	SUR8840G
SS5P10-M3/86A	STEP_VOLTAGE	SUP45P03-09-GE3	SURA8110T3G
SS5P6-M3/86A	STEPPER_FULLSTEP _2PHASE	SUP50020EL-GE3	SURA8120T3G
SS8P3L-M3/86A	STEPPER_HALFSTEP _2PHASE	SUP50N03-5M1P- GE3	SURA8130T3G
SS8PH10-M3/86A		SUP53P06-20-GE3	SURA8140T3G
SSA24-E3/61T	STEPPER_MOTOR_ 2PHASE	SUP57N20-33-E3	SURA8160T3G
SSA33L-E3/61T		SUP60030E-GE3	SURA8210T3G
SSA34-E3/61T	STEPPER_MOTOR_ 2PHASE_2WINDING	SUP60N10-16L-E3	SURA8215T3G
SSC53L-E3/57T	STEPPER_WAVE_2P HASE	SUP70040E-GE3	SURA8220T3G
SSC54-E3/57T		SUP75P03-07-E3	SURA8240T3G
SSM2017P	STF202-22T1G	SUP80090E-GE3	SURB1620CTT4G
SSM2017S	STP32N06L	SUP85N03-3M6P- GE3	SURD8320T4G
SSM2135S	SUD17N25-165-E3	SUP85N10-10-E3	SURD8330T4G
SSM2212RZ	SUD20N10-66L-GE3	SUP85N15-21-E3	SURD8530T4G
SSM2212RZ-R7	SUM110N10-09-E3	SUP90N03-03-E3	SURHB8840CTT4G
SSM2212RZ-RL	SUM120N04-1m7L- GE3	SUP90N04-3M3P- GE3	SURHD8560T4G
SSRD8620CTRG	SUM40010EL-GE3	SUP90P06-09L-E3	SURHD8560W1T4G
SSRD8620CTT4G	SUM50020EL-GE3		SURHS8160T3G
SSRD8620CTT4RG	SUM60030E-GE3	SUR620CTT4G	SURS340DT3G
ST5771-1	SUM70040E-GE3	SUR81520G	SURS360DBT3G
STD110N02RT4G	SUM80090E-GE3	SUR81560G	SURS360DT3G
STD24N06LT4G	SUM85N15-19-E3	SUR83020PTG	SURS8105T3G
STD2955T4G			SURS8110T3G

Multisim 14.1 Education Components

SURS8115T3G	SYNCHRONOUS_M	SZ1SMB28AT3G	SZBZX84C15LT1G
SURS8120T3G	ACHINE_PERMANE	SZ1SMB28CAT3G	SZBZX84C15LT3G
SURS8140T3G	NT_MAGNET_E	SZ1SMB30AT3G	SZBZX84C33LT1G
SURS8160T3G	SYNCHRONOUS_M	SZ1SMB30CAT3G	SZBZX84C33LT3G
SURS8205T3G	ACHINE_PERMANE	SZ1SMB33CAT3G	SZBZX84C36LT1G
SURS8210T3G	NT_MAGNET_HALL	SZ1SMB5.0AT3G	SZBZX84C3V0LT1G
SURS8220T3G	SZ1.5SMC15AT3G	SZ1SMB58CAT3G	SZBZX84C4V7LT1G
SURS8320T3G	SZ1.5SMC20AT3G	SZ1SMB5918BT3G	SZBZX84C4V7LT3G
SURS8340T3G	SZ1.5SMC33AT3G	SZ1SMB5919BT3G	SZBZX84C5V1LT1G
SURS8360BT3G	SZ1.5SMC39AT3G	SZ1SMB5920BT3G	SZBZX84C5V1LT3G
SURS8360T3G	SZ1.5SMC43AT3G	SZ1SMB5921BT3G	SZBZX84C5V6LT1G
SWHYSTE	SZ1.5SMC62AT3G	SZ1SMB5922BT3G	SZBZX84C5V6LT3G
Switch1	SZ1SMA30AT3G	SZ1SMB5924BT3G	SZBZX84C68LT1G
SXT2222A	SZ1SMA40CAT3G	SZ1SMB5925BT3G	SZBZX84C6V2LT1G
SXT2907A	SZ1SMA5913BT3G	SZ1SMB5927BT3G	SZBZX84C6V2LT3G
SXT3904	SZ1SMA5918BT3G	SZ1SMB5931BT3G	SZBZX84C6V8LT1G
SXT3906	SZ1SMA5921BT3G	SZ1SMB5933BT3G	SZBZX84C6V8LT3G
SXTA42	SZ1SMA5922BT3G	SZ1SMB5934BT3G	SZBZX84C75LT1G
SXTA43	SZ1SMA5927BT3G	SZ1SMB5935BT3G	SZBZX84C9V1LT1G
SXTA92	SZ1SMA5932BT3G	SZ1SMB5936BT3G	SZBZX84C9V1LT3G
SXTA93	SZ1SMA5936BT3G	SZ1SMB5937BT3G	SZESD5Z5.0T1G
SYNCHRONOUS_M	SZ1SMA5940BT3G	SZ1SMB5939BT3G	SZESD5Z7.0T1G
ACHINE_PERMANE	SZ1SMB14AT3G	SZ1SMC36AT3G	SZESD9B5.0ST5G
NT_MAGNET	SZ1SMB24AT3G	SZBZX84B16LT1G	SZMM3Z10VT1G
	SZ1SMB24CAT3G	SZBZX84C12LT1G	SZMM3Z12VST1G
	SZ1SMB26CAT3G		

Multisim 14.1 Education Components

SZMM3Z15VT1G	SZMM5Z5V6T1G	SZMMBZ5242BLT1 G	SZMMSZ4705T1G
SZMM3Z18VT1G	SZMM5Z6V2ST1G	SZMMBZ5248BLT1 G	SZMMSZ4715T1G
SZMM3Z20VT1G	SZMM5Z6V8ST1G	SZMMBZ5254BLT1 G	SZMMSZ5221BT1G
SZMM3Z2V4T1G	SZMM5Z6V8T1G	SZMMBZ5256BLT1 G	SZMMSZ5225BT1G
SZMM3Z3V3ST1G	SZMM5Z7V5T1G	SZMMBZ5256BLT1 G	SZMMSZ5226BT1G
SZMM3Z3V6T1G	SZMM5Z8V2ST1G	SZMMBZ5256BLT1 G	SZMMSZ5228BT1G
SZMM3Z43VT1G	SZMM5Z8V2T1G	SZMMBZ5V6ALT1G	SZMMSZ5231BT1G
SZMM3Z4V3ST1G	SZMMBZ15VDLT1G	SZMMQA15VT1G	SZMMSZ5234BT1G
SZMM3Z4V7T1G	SZMMBZ15VDLT3G	SZMMQA5V6T1G	SZMMSZ5235BT1G
SZMM3Z5V1T1G	SZMMBZ20VALT1G	SZMMQA6V2T1G	SZMMSZ5236BT1G
SZMM3Z5V6ST1G	SZMMBZ27VALT1G	SZMMSZ10T1G	SZMMSZ5239BT1G
SZMM5Z10VT1G	SZMMBZ27VALT3G	SZMMSZ12T1G	SZMMSZ5240BT1G
SZMM5Z12VT1G	SZMMBZ27VCLT1G	SZMMSZ2V7T1G	SZMMSZ5242BT1G
SZMM5Z16VT1G	SZMMBZ33VALT1G	SZMMSZ3V3T1G	SZMMSZ5242BT3G
SZMM5Z18VT1G	SZMMBZ5221BLT1 G	SZMMSZ4678T1G	SZMMSZ5243BT1G
SZMM5Z20VT1G	SZMMBZ5222BLT1 G	SZMMSZ4683T1G	SZMMSZ5245BT1G
SZMM5Z24VT1G	SZMMBZ5226BLT1 G	SZMMSZ4688T1G	SZMMSZ5246BT1G
SZMM5Z27VT1G	SZMMBZ5231BLT1 G	SZMMSZ4689T1G	SZMMSZ5254BT1G
SZMM5Z36VT1G	SZMMBZ5231BLT1 G	SZMMSZ4690T1G	SZMMSZ5258BT1G
SZMM5Z3V0T1G	SZMMBZ5231BLT3 G	SZMMSZ4690T3G	SZMMSZ5258BT3G
SZMM5Z3V3T1G	SZMMBZ5232BLT1 G	SZMMSZ4691T1G	SZMMSZ5259BT1G
SZMM5Z4V7ST1G	SZMMBZ5232BLT1 G	SZMMSZ4692T1G	SZMMSZ5260BT1G
SZMM5Z4V7ST5G	SZMMBZ5240BLT1 G	SZMMSZ4696T1G	SZMMSZ5262BT1G
SZMM5Z5V1T1G	SZMMBZ5240BLT1 G	SZMMSZ4699T1G	SZMSQA6V1W5T2G
SZMM5Z5V6ST1G			SZNUP1105LT1G

Multisim 14.1 Education Components

SZNUP1301ML3T1G	TC1410EPA	TC1412CPA	TC4420VAT
SZNUP2105LT1G	TC1410EUA	TC1412EOA	TC4420VMF
SZNUP4301MR6T1 G	TC1410NCOA	TC1412EPA	TC4420VOA
	TC1410NCPA	TC1412EUA	TC4420VPA
SZNUP4304MR6T1 G	TC1410NEOA	TC1412NCOA	TC4421AVMF
SZNZ9F2V7ST5G	TC1410NEPA	TC1412NCPA	TC4421CAT
SZNZ9F6V2ST5G	TC1410NEUA	TC1412NEOA	TC4421CPA
SZP6SMB15AT3G	TC1410NVUA	TC1412NEPA	TC4421EMF713
SZP6SMB18AT3G	TC1411COA	TC1412NEUA	TC4421EPA
SZP6SMB20AT3G	TC1411CPA	TC4404COA	TC4421ESM
SZP6SMB33AT3G	TC1411EOA	TC4404CPA	TC4421MJA
SZP6SMB43CAT3G	TC1411EPA	TC4404EOA	TC4421VAT
SZP6SMB51AT3G	TC1411EUA	TC4404EPA	TC4421VMF
SZP6SMB6.8AT3G	TC1411NCOA	TC4405COA	TC4421VPA
SZP6SMB62AT3G	TC1411NCPA	TC4405CPA	TC4422CAT
SZSMF12CT1G	TC1411NEOA	TC4405EOA	TC4422CPA
SZSMF33AT1G	TC1411NEPA	TC4405EPA	TC4422EAT
T_FF	TC1411NEUA	TC4420CAT	TC4422EPA
T_FF_NEGSR	TC1411NVOA	TC4420COA	TC4422ESM
TBASE_TIMER_TOF F	TC1411NVPA	TC4420CPA	TC4422MJA
	TC1411NVUA	TC4420EMF	TC4422VAT
TBASE_TIMER_TON	TC1411VOA	TC4420EOA	TC4422VMF
TC1410COA	TC1411VPA	TC4420EPA	TC4422VPA
TC1410CPA	TC1411VUA	TC4420IJA	TC4423AVMF
TC1410EOA	TC1412COA	TC4420MJA	TC4423AVOA

Multisim 14.1 Education Components

TC4423AVOE	TC4425AVOE	TC4427EOA	TC4429VMF
TC4423AVPA	TC4425AVPA	TC4427EPA	TC4429VOA
TC4423COE	TC4425COE	TC4427EUA713	TC4429VPA
TC4423CPA	TC4425CPA	TC4427VMF	TC4431COA
TC4423EOE	TC4425EOE	TC4427VOA	TC4431CPA
TC4423EPA	TC4425EPA	TC4427VUA	TC4431EOA
TC4423MJA	TC4425VMF	TC4428ACOA713	TC4431EPA
TC4423VMF	TC4425VOE	TC4428AEJA	TC4431VOA
TC4423VOE	TC4425VPA	TC4428AEOA713	TC4431VPA
TC4423VPA	TC4426ACOA713	TC4428AMJA	TC4432COA
TC4424AVMF	TC4426AEOA713	TC4428COA	TC4432CPA
TC4424AVOA	TC4426COA	TC4428CPA	TC4432EOA
TC4424AVOE	TC4426CPA	TC4428EMF	TC4432EPA
TC4424AVPA	TC4426EMF	TC4428EOA	TC4432VOA
TC4424COE	TC4426EOA	TC4428EPA	TC4432VPA
TC4424CPA	TC4426EPA	TC4428EUA	TC4451VAT
TC4424EMF	TC4426EUA	TC4428VMF	TC4451VMF
TC4424EOE	TC4426MJA	TC4428VOA	TC4451VOA
TC4424EPA	TC4426VMF	TC4428VUA	TC4451VPA
TC4424MJA	TC4426VUA	TC4429COA713	TC4452VAT
TC4424VMF	TC4427ACOA713	TC4429EMF	TC4452VMF
TC4424VOE	TC4427AEOA713	TC4429EOA713	TC4452VOA
TC4424VPA	TC4427COA	TC4429IJA	TC4452VPA
TC4425AVMF	TC4427CPA	TC4429MJA	TC4467COE
TC4425AVOA	TC4427EMF	TC4429VAT	TC4467CPD

Multisim 14.1 Education Components

TC4467EOE713	TDZ12J	TEMD1000	TF410-TL-H
TC4468COE	TDZ13J	TEMD1020	TF412ST5G
TC4468CPD	TDZ15J	TEMD1030	TF414T5G
TC4468EOE713	TDZ16J	TEMD5010X01	TFPT0603L1000DV
TC4468MOE	TDZ18J	TEMD5020X01	TFPT0603L1000FV
TC4469COE	TDZ20J	TEMD5110X01	TFPT0603L1000JV
TC4469CPD	TDZ22J	TEMD5510FX01	TFPT0603L1001DV
TC4469EJD	TDZ24J	TEMD6010FX01	TFPT0603L1001FV
TC4469MJD	TDZ27J	TEMP_NC	TFPT0603L1001JV
TCET1100	TDZ2V4J	TEMP_NO	TFPT0603L1200DV
TCET1100G	TDZ2V7J	TEMPERATURE_SOURCE	TFPT0603L1200FV
TCET1600	TDZ30J	TEMPLATE_1P1S_TMODEL	TFPT0603L1200JV
TCET1600G	TDZ3V0J	TEMPLATE_1P2S_COUPLED	TFPT0603L1500DV
TCLT1003	TDZ3V3J	TEMPLATE_1P2S_NON_LINEAR	TFPT0603L1500FV
TCMT1103	TDZ3V6J	TEMPLATE_1P2S_TAP_TMODEL	TFPT0603L1500JV
TCMT1600	TDZ3V9J	TEMPLATE_1P2S_TMODEL	TFPT0603L1800DV
TCMT4600	TDZ4V3J	TEMPLATE_1P2S_TMODEL	TFPT0603L1800FV
TD_SW1	TDZ4V7J	TEST_LABEL	TFPT0603L1800JV
TD4A	TDZ5V1J	TEST_PT_SMT	TFPT0603L2200DV
TD5A	TDZ5V6J	TEST_PT_THT	TFPT0603L2200FV
TDA2030	TDZ6V2J	TF408-2-TL-H	TFPT0603L2200JV
TDM_CURRENT	TDZ6V8J	TF408-3-TL-H	TFPT0603L2700DV
TDM_VOLTAGE	TDZ7V5J		TFPT0603L2700FV
TDZ10J	TDZ8V2J		TFPT0603L2700JV
TDZ11J	TDZ9V1J		TFPT0603L3300DV

Multisim 14.1 Education Components

TFPT0603L3300FV	TFPT0805L1200JV	TFPT0805L2701DV	TFPT0805L5600FV
TFPT0603L3300JV	TFPT0805L1201DV	TFPT0805L2701FV	TFPT0805L5600JV
TFPT0603L3900DV	TFPT0805L1201FV	TFPT0805L2701JV	TFPT0805L6800DV
TFPT0603L3900FV	TFPT0805L1201JV	TFPT0805L3300DV	TFPT0805L6800FV
TFPT0603L3900JV	TFPT0805L1500DV	TFPT0805L3300FV	TFPT0805L6800JV
TFPT0603L4700DV	TFPT0805L1500FV	TFPT0805L3300JV	TFPT0805L8200DV
TFPT0603L4700FV	TFPT0805L1500JV	TFPT0805L3301DV	TFPT0805L8200FV
TFPT0603L4700JV	TFPT0805L1501DV	TFPT0805L3301FV	TFPT0805L8200JV
TFPT0603L5600DV	TFPT0805L1501FV	TFPT0805L3301JV	TFPT1206L1000DV
TFPT0603L5600FV	TFPT0805L1501JV	TFPT0805L3900DV	TFPT1206L1000FV
TFPT0603L5600JV	TFPT0805L1800DV	TFPT0805L3900FV	TFPT1206L1000JV
TFPT0603L6800DV	TFPT0805L1800FV	TFPT0805L3900JV	TFPT1206L1001DV
TFPT0603L6800FV	TFPT0805L1800JV	TFPT0805L3901DV	TFPT1206L1001FV
TFPT0603L6800JV	TFPT0805L1801DV	TFPT0805L3901FV	TFPT1206L1001JV
TFPT0603L8200DV	TFPT0805L1801FV	TFPT0805L3901JV	TFPT1206L1002DV
TFPT0603L8200FV	TFPT0805L1801JV	TFPT0805L4700DV	TFPT1206L1002FV
TFPT0603L8200JV	TFPT0805L2200DV	TFPT0805L4700FV	TFPT1206L1002JV
TFPT0805L1000DV	TFPT0805L2200FV	TFPT0805L4700JV	TFPT1206L1200DV
TFPT0805L1000FV	TFPT0805L2200JV	TFPT0805L4701DV	TFPT1206L1200FV
TFPT0805L1000JV	TFPT0805L2201DV	TFPT0805L4701FV	TFPT1206L1200JV
TFPT0805L1001DV	TFPT0805L2201FV	TFPT0805L4701JV	TFPT1206L1201DV
TFPT0805L1001FV	TFPT0805L2201JV	TFPT0805L5001DV	TFPT1206L1201FV
TFPT0805L1001JV	TFPT0805L2700DV	TFPT0805L5001FV	TFPT1206L1201JV
TFPT0805L1200DV	TFPT0805L2700FV	TFPT0805L5001JV	TFPT1206L1500DV
TFPT0805L1200FV	TFPT0805L2700JV	TFPT0805L5600DV	TFPT1206L1500FV

Multisim 14.1 Education Components

TFPT1206L1500JV	TFPT1206L3301DV	TFPT1206L6800FV	THS3062DGN
TFPT1206L1501DV	TFPT1206L3301FV	TFPT1206L6800JV	THS3091D
TFPT1206L1501FV	TFPT1206L3301JV	TFPT1206L6801DV	THS3091DDA
TFPT1206L1501JV	TFPT1206L3900DV	TFPT1206L6801FV	THS3092D
TFPT1206L1800DV	TFPT1206L3900FV	TFPT1206L6801JV	THS3092DDA
TFPT1206L1800FV	TFPT1206L3900JV	TFPT1206L8200DV	THS3095D
TFPT1206L1800JV	TFPT1206L3901DV	TFPT1206L8200FV	THS3095DDA
TFPT1206L1801DV	TFPT1206L3901FV	TFPT1206L8200JV	THS3096D
TFPT1206L1801FV	TFPT1206L3901JV	TFPT1206L8201DV	THS3096PWP
TFPT1206L1801JV	TFPT1206L4700DV	TFPT1206L8201FV	THS3110DGN
TFPT1206L2200DV	TFPT1206L4700FV	TFPT1206L8201JV	THS3110ID
TFPT1206L2200FV	TFPT1206L4700JV	THERMAL_NOISE	THS3110IDGN
TFPT1206L2200JV	TFPT1206L4701DV	THERMAL_OL	THS3110IDR
TFPT1206L2201DV	TFPT1206L4701FV	THERMAL_OL_RELAY	THS3111CD
TFPT1206L2201FV	TFPT1206L4701JV		THS3111CDGNR
TFPT1206L2201JV	TFPT1206L5001DV	THREE_PHASE_DELTA	THS3111DGN
TFPT1206L2700DV	TFPT1206L5001FV	THREE_PHASE_WYE	THS3111ID
TFPT1206L2700FV	TFPT1206L5001JV	THS3001CD	THS3111IDGN
TFPT1206L2700JV	TFPT1206L5600DV	THS3001CDGN	THS3112CD
TFPT1206L2701DV	TFPT1206L5600FV	THS3001ID	THS3112CDDA
TFPT1206L2701FV	TFPT1206L5600JV	THS3001IDGN	THS3112ID
TFPT1206L2701JV	TFPT1206L5601DV	THS3061D	THS3112IDDA
TFPT1206L3300DV	TFPT1206L5601FV	THS3061DGN	THS3120CDGN
TFPT1206L3300FV	TFPT1206L5601JV	THS3062D	THS3120DGN
TFPT1206L3300JV	TFPT1206L6800DV	THS3062DDA	THS3120ID

Multisim 14.1 Education Components

THS3120IDGN	THS4012ID	THS4042ID	THS4081IDGN
THS3121CD	THS4021CD	THS4042IDGN	THS4082CD
THS3121ID	THS4021CDGN	THS4051CD	THS4082CDGN
THS3121IDGN	THS4021ID	THS4051CDGN	THS4082ID
THS3122CD	THS4021IDGN	THS4051ID	THS4082IDGN
THS3122CDDA	THS4022CD	THS4051IDGN	THS4120CD
THS3122ID	THS4022CDGN	THS4051MFK	THS4120CDGK
THS3122IDDA	THS4022ID	THS4051MJG	THS4121CD
THS3125CPWP	THS4022IDGN	THS4052CD	THS4121CDGK
THS3125ID	THS4031CD	THS4052CDGN	THS4130CD
THS3125IPWP	THS4031CDGN	THS4052ID	THS4130CDGK
THS3201D	THS4031ID	THS4052IDGN	THS4130ID
THS3201DBVT	THS4031IDGN	THS4061CD	THS4130IDGK
THS3201DGK	THS4031MFK	THS4061CDGN	THS4131CD
THS3202D	THS4031MJG	THS4061ID	THS4131CDGK
THS3202DGK	THS4032CD	THS4061IDGN	THS4131ID
THS3202DGN	THS4032CDGN	THS4061MFK	THS4131IDGK
THS4001CD	THS4032ID	THS4061MJG	THS4140CD
THS4001ID	THS4032IDGN	THS4062CD	THS4140CDGK
THS4011CD	THS4041CD	THS4062CDGN	THS4140ID
THS4011CDGN	THS4041CDGN	THS4062ID	THS4140IDGK
THS4011ID	THS4041ID	THS4062IDGN	THS4141CD
THS4011MFKB	THS4041IDGN	THS4081CD	THS4141CDGK
THS4012CD	THS4042CD	THS4081CDGN	THS4141ID
THS4012CDGN	THS4042CDGN	THS4081ID	THS4141IDGK

Multisim 14.1 Education Components

THS4150CD	THS4226DGQ	THS4501IDGN	THS4531IDGK
THS4150CDGK	THS4271D	THS4502CD	THS4531IRUNT
THS4150ID	THS4271DGK	THS4502CDGK	THS4532IPW
THS4150IDGK	THS4271DGN	THS4502ID	THS4541IRGTR
THS4151CD	THS4271DR	THS4502IDGK	THS4541IRUNR
THS4151CDGK	THS4271DRBT	THS4503CD	THS4601CD
THS4151ID	THS4281D	THS4503CDGK	THS4601CDDA
THS4151IDGK	THS4281DBVR	THS4503CDGN	THS4601CDG4
THS4211D	THS4281DGK	THS4503ID	THS4601ID
THS4211DGK	THS4302RGTT	THS4503IDGK	THS4601IDDA
THS4211DGN	THS4303RGTT	THS4503IDGN	THS4601IDG4
THS4215D	THS4304D	THS4504D	THS4631D
THS4215DGK	THS4304DBVT	THS4504DGK	THS4631DDA
THS4215DGN	THS4304DGK	THS4504DGN	THS4631DGN
THS4215DRBT	THS4500CD	THS4505D	THS6002CDWP
THS4221D	THS4500CDGK	THS4505DGK	THS6002IDWP
THS4221DBV	THS4500CDGN	THS4508RGTR	THS6007IPWP
THS4221DGK	THS4500ID	THS4509RGT	THS6012CDWP
THS4221DGN	THS4500IDGK	THS4511RGTT	THS6012IDWP
THS4222D	THS4500IDGN	THS4513RGTR	THS6012IGQER
THS4222DGK	THS4501CD	THS4520RGTR	THS6022CPWP
THS4222DGN	THS4501CDGK	THS4531AID	THS6022IPWP
THS4225D	THS4501CDGN	THS4531AIDGK	THS6032CDWP
THS4225DGK	THS4501ID	THS4531AIRUNT	THS6032IDWP
THS4225DGN	THS4501IDGK	THS4531ID	THS6032IVFPG4

Multisim 14.1 Education Components

THS6042CDDA	THS6093CPWP	TIMED_NCTO	TIP125G
THS6042ID	THS6093ID	TIMED_NOTC	TIP126G
THS6042IDDA	THS6093IPWP	TIMED_NOTO	TIP127G
THS6043CD	THS6182D	TIMER_TOFF	TIP140G
THS6043CPWP	THS6182DW	TIMER_TON	TIP141G
THS6043ID	THS6182DWP	TIMER_TON_RETEN TION	TIP142G
THS6043IPWP	THS6182RHFR		TIP147G
THS6052CD	THS6184PWP	TIMER_TON_RETEN TION_HOLD_RESET	TIP2955G
THS6052CDDA	THS6184RHFR	TIMER_TON_RETEN TION_RESET	TIP29AG
THS6052ID	THS7001CPWP		TIP29BG
THS6052IDDA	THS7001IPWP	TI-MSP430-HDR	TIP29CG
THS6053CPWPR	THS7002CPWP	TIP100G	TIP3055G
THS6053ID	THS7002IPWP	TIP101G	TIP30CG
THS6053IPWP	THS7530PWP	TIP102G	TIP31AG
THS6062CD	TIME_DELAY_1A	TIP106G	TIP31BG
THS6062CDGN	TIME_DELAY_1C	TIP107G	TIP31CG
THS6062ID	TIME_DELAY_2A	TIP110G	TIP31G
THS6062IDGN	TIME_DELAY_2C	TIP111G	TIP32AG
THS6072CD	TIME_DELAY_3A	TIP112G	TIP32BG
THS6072CDGN	TIME_DELAY_3C	TIP115G	TIP32CG
THS6072ID	TIME_DELAY_4A	TIP116G	TIP32G
THS6072IDGNR	TIME_DELAY_4C	TIP117G	TIP33CG
THS6092CDDA	TIME_DELAY_NC	TIP120G	TIP35AG
THS6092ID	TIME_DELAY_NO	TIP121G	TIP35CG
THS6092IDDA	TIMED_NCTC	TIP122G	TIP36AG

Multisim 14.1 Education Components

TIP36CG	TL031AMFK	TL032MJG	TL051ACP
TIP41AG	TL031AMJG	TL032ML	TL051AID
TIP41BG	TL031AML	TL032MP	TL051AIP
TIP41CG	TL031AMP	TL034ACD	TL051AMD
TIP42AG	TL031ID	TL034ACN	TL051AMFK
TIP42BG	TL031IP	TL034AID	TL051AMJG
TIP42CG	TL031MD	TL034AIN	TL051AML
TIP42G	TL031MFK	TL034AMD	TL051AMP
TIP47G	TL031MJG	TL034AMFK	TL051CD
TIP48G	TL031MP	TL034AMJ	TL051CP
TIP50G	TL032ACD	TL034AMN	TL051ID
TIS92	TL032ACP	TL034CD	TL051IP
TIS93	TL032AID	TL034CN	TL051MD
TIS97	TL032AIP	TL034ID	TL051MFK
TIS98	TL032AMD	TL034IN	TL051MJG
TIS99	TL032AMFK	TL034MD	TL051ML
TL022CD	TL032AMJG	TL034MFK	TL051MP
TL022CP	TL032AMJL	TL034MJ	TL052ACD
TL022MJG	TL032AMP	TL034MN	TL052ACP
TL022MU	TL032CD	TL044CJ	TL052AID
TL031ACD	TL032CP	TL044CN	TL052AIP
TL031ACP	TL032ID	TL044MFK	TL052AMD
TL031AID	TL032IP	TL044MJ	TL052AMFK
TL031AIP	TL032MD	TL044MW	TL052AMJG
TL031AMD	TL032MFK	TL051ACD	TL052AML

Multisim 14.1 Education Components

TL052AMP	TL054MN	TL062IP	TL066MFK
TL052CD	TL061ACD	TL062IPW	TL066MJG
TL052CP	TL061ACP	TL062MFK	TL070ACD
TL052ID	TL061BCD	TL062MJG	TL070ACJG
TL052IP	TL061BCP	TL062ML	TL070ACP
TL052MD	TL061CD	TL062MU	TL070CD
TL052MFK	TL061CP	TL064ACD	TL070CJG
TL052MJG	TL061ID	TL064ACN	TL070CP
TL052ML	TL061IP	TL064BCD	TL070CPW
TL052MP	TL061MFK	TL064BCN	TL070ID
TL054ACD	TL061MJG	TL064CD	TL070IJG
TL054ACN	TL061ML	TL064CN	TL070IP
TL054AID	TL061MU	TL064CNSR	TL070MD
TL054AIN	TL061VD	TL064CPW	TL070MP
TL054AMD	TL061VP	TL064ID	TL071ACD
TL054AMFK	TL062ACD	TL064IN	TL071ACJG
TL054AMJ	TL062ACP	TL064MFK	TL071ACP
TL054AMN	TL062ACPSR	TL064MJ	TL071BCD
TL054CD	TL062BCD	TL064MW	TL071BCP
TL054CN	TL062BCP	TL066ACD	TL071CD
TL054ID	TL062CD	TL066ACP	TL071CJG
TL054IN	TL062CP	TL066CD	TL071CP
TL054MD	TL062CPSR	TL066CP	TL071CPWLE
TL054MFK	TL062CPW	TL066ID	TL071ID
TL054MJ	TL062ID	TL066IP	TL071IP

Multisim 14.1 Education Components

TL071MFK	TL074CN	TL081IJG	TL084MFK
TL071MJG	TL074CPWLE	TL081IP	TL084MJ
TL071ML	TL074ID	TL081MFK	TL085
TL072ACD	TL074IN	TL081MJG	TL087CD
TL072ACP	TL074MFK	TL081MU	TL087CJG
TL072ACPSR	TL074MJ	TL082CD	TL087CL
TL072BCD	TL074MN	TL082CM	TL087CP
TL072BCP	TL074MW	TL082CP	TL087ID
TL072CD	TL075	TL082ID	TL087IJG
TL072CP	TL075CN	TL082IP	TL087IL
TL072CPSR	TL080CD	TL082IPWR	TL087IP
TL072CPW	TL080CP	TL082MFK	TL088CD
TL072CPWLE	TL080M	TL082MJG	TL088CJG
TL072ID	TL081ACD	TL083	TL088CL
TL072IP	TL081ACJG	TL084ACD	TL088CP
TL072MFK	TL081ACP	TL084ACN	TL088ID
TL072MJG	TL081AMJG	TL084ACNSR	TL088IJG
TL072MJGB	TL081BCD	TL084BCD	TL088IL
TL072ML	TL081BCJG	TL084BCN	TL088IP
TL072MP	TL081BCP	TL084CD	TL088MJG
TL074ACD	TL081CD	TL084CN	TL088ML
TL074ACN	TL081CJG	TL084CNSR	TL088MU
TL074BCD	TL081CP	TL084CPW	TL136
TL074BCN	TL081CPW	TL084ID	TL136N
TL074CD	TL081ID	TL084IN	TL1963ADCQR

Multisim 14.1 Education Components

TL1963AKTTR	TL34071D	TL431BCD	TLC071ID
TL287CD	TL34071P	TL431BCLP	TLC071IP
TL287CJG	TL3472CD	TL431BCP	TLC074CD
TL287CL	TL3472CP	TL431ID	TLC074CN
TL287CP	TL3472ID	TL431IDBVR	TLC074CPWP
TL288CD	TL3472IP	TL431IDBZR	TLC081CD
TL288CJG	TL3474CD	TL431ILP	TLC081CP
TL288CL	TL3474CN	TL431ILPR	TLC081ID
TL288CP	TL3474CPW	TL431IP	TLC081IP
TL288MJG	TL3474ID	TL431IPK	TLC1078CD
TL288ML	TL3474IN	TL431QD	TLC1078CP
TL288MU	TL3474IPW	TL431QDBVR	TLC1078ID
TL321CD	TL35071D	TL431QDBZR	TLC1078IP
TL321CP	TL35071P	TL431QDCKR	TLC1078MD
TL321ID	TL431ACD	TL431QPK	TLC1078MFK
TL321IP	TL431ACDBVR	TL972ID	TLC1078MJG
TL322CD	TL431ACDBZR	TL972IDGKR	TLC1078MP
TL322CDR	TL431ACDCKR	TL972IP	TLC1079CD
TL322CP	TL431ACL P	TL972IPW	TLC1079CN
TL322ID	TL431ACLPM	TLC070CD	TLC1079ID
TL322IP	TL431ACLPR	TLC070CP	TLC1079IN
TL33071D	TL431ACP	TLC070ID	TLC1079MD
TL33071P	TL431ACPK	TLC070IP	TLC1079MFK
TL331IDBVR	TL431ACPSR	TLC071CD	TLC1079MJ
TL331KDBVR	TL431ACPW	TLC071CP	TLC1079MN

Multisim 14.1 Education Components

TLC2201ACD	TLC2202CD	TLC2262CP	TLC2274MFK
TLC2201ACP	TLC2202CP	TLC2262CPWLE	TLC2274MJ
TLC2201AID	TLC2202ID	TLC2262MFK	TLC2274MN
TLC2201AIP	TLC2202IP	TLC2262MJG	TLC251ACD
TLC2201BCD	TLC2202MD	TLC2262MU	TLC251ACP
TLC2201BCP	TLC2202MFK	TLC2264CD	TLC251BCD
TLC2201BID	TLC2202MJG	TLC2264CN	TLC251BCP
TLC2201BIP	TLC2202MP	TLC2264CPW	TLC251CD
TLC2201CD	TLC2202Y	TLC2264CPWLE	TLC251CP
TLC2201CP	TLC2252AID	TLC2264MFK	TLC251Y
TLC2201ID	TLC2252AIP	TLC2264MJ	TLC252ACD
TLC2201IP	TLC2252AIPWLE	TLC2264MW	TLC252ACP
TLC2201MD	TLC2252CD	TLC2272ACD	TLC252ACPW
TLC2201MFK	TLC2252CP	TLC2272ACP	TLC252BCD
TLC2201MJG	TLC2252CPWLE	TLC2272CD	TLC252BCP
TLC2201MP	TLC2252MFK	TLC2272CP	TLC252BCPW
TLC2201Y	TLC2252MJG	TLC2272CPWLE	TLC252CD
TLC2202ACD	TLC2252MU	TLC2272Y	TLC252CP
TLC2202ACP	TLC2254CD	TLC2274ACD	TLC252CPW
TLC2202AID	TLC2254CN	TLC2274ACN	TLC254ACD
TLC2202AIP	TLC2254CPWLE	TLC2274ACPW	TLC254ACN
TLC2202BCD	TLC2254MFK	TLC2274CD	TLC254BCD
TLC2202BCP	TLC2254MJ	TLC2274CN	TLC254BCN
TLC2202BID	TLC2254MW	TLC2274CPWLE	TLC254CD
TLC2202BIP	TLC2262CD	TLC2274MD	TLC254CN

Multisim 14.1 Education Components

TLC254CPW	TLC2652AM-14D	TLC2654ACN	TLC2654MJ
TLC25L2ACD	TLC2652AM-8D	TLC2654ACP	TLC2654MJG
TLC25L2ACP	TLC2652AMFK	TLC2654AI-14D	TLC2654MN
TLC25L2BCD	TLC2652AMJ	TLC2654AID	TLC2654MP
TLC25L2BCP	TLC2652AMJG	TLC2654AIN	TLC271ACD
TLC25L2CD	TLC2652AMN	TLC2654AIP	TLC271ACP
TLC25L2CP	TLC2652AMP	TLC2654AM-14D	TLC271AID
TLC25L4CD	TLC2652C-14D	TLC2654AM-8D	TLC271AIP
TLC25L4CN	TLC2652C-8D	TLC2654AMF	TLC271BCD
TLC25M2ACD	TLC2652CN	TLC2654AMFK	TLC271BCP
TLC25M2ACP	TLC2652CP	TLC2654AMJ	TLC271BID
TLC25M2BCD	TLC2652I-14D	TLC2654AMJG	TLC271BIP
TLC25M2BCP	TLC2652ID	TLC2654AMN	TLC271CD
TLC25M2CD	TLC2652IN	TLC2654AMP	TLC271CP
TLC25M2CP	TLC2652IP	TLC2654C-14D	TLC271ID
TLC25M4CD	TLC2652M-14D	TLC2654C-8D	TLC271IP
TLC25M4CN	TLC2652M-8D	TLC2654CN	TLC271MD
TLC2652AC-14D	TLC2652MFK	TLC2654CP	TLC271MFK
TLC2652AC-8D	TLC2652MJ	TLC2654I-14D	TLC271MJG
TLC2652ACN	TLC2652MJG	TLC2654I-8D	TLC271MP
TLC2652ACP	TLC2652MN	TLC2654IN	TLC272CD
TLC2652AI-14D	TLC2652MP	TLC2654IP	TLC272CP
TLC2652AI-8D	TLC2652Y	TLC2654M-14D	TLC272CPW
TLC2652AIN	TLC2654AC-14D	TLC2654M-8D	TLC272ID
TLC2652AIP	TLC2654AC-8D	TLC2654MFK	TLC272IP

Multisim 14.1 Education Components

TLC272MD	TLC279MD	TLC27L4BCN	TLC27L9MJ
TLC272MFK	TLC279MFK	TLC27L4BID	TLC27L9MP
TLC272MJG	TLC279MJ	TLC27L4BIN	TLC27M2ACD
TLC272MP	TLC279MN	TLC27L4CD	TLC27M2ACP
TLC274CD	TLC27L2ACD	TLC27L4CN	TLC27M2AID
TLC274CN	TLC27L2ACP	TLC27L4ID	TLC27M2AIP
TLC274CPW	TLC27L2AID	TLC27L4IN	TLC27M2BCD
TLC274ID	TLC27L2AIP	TLC27L4MD	TLC27M2BCP
TLC274IN	TLC27L2BCD	TLC27L4MFK	TLC27M2BID
TLC274MD	TLC27L2BCP	TLC27L4MJ	TLC27M2BIP
TLC274MFK	TLC27L2BID	TLC27L4MN	TLC27M2CD
TLC274MJ	TLC27L2BIP	TLC27L7CD	TLC27M2CP
TLC274MN	TLC27L2CD	TLC27L7CP	TLC27M2ID
TLC277CD	TLC27L2CP	TLC27L7ID	TLC27M2IP
TLC277CP	TLC27L2ID	TLC27L7IP	TLC27M2MD
TLC277ID	TLC27L2IP	TLC27L7MD	TLC27M2MFK
TLC277IP	TLC27L2MD	TLC27L7MFK	TLC27M2MJG
TLC277MD	TLC27L2MFK	TLC27L7MJG	TLC27M2MP
TLC277MFK	TLC27L2MJG	TLC27L7MP	TLC27M4ACD
TLC277MJG	TLC27L2MP	TLC27L9CD	TLC27M4ACN
TLC277MP	TLC27L4ACD	TLC27L9CN	TLC27M4AID
TLC279CD	TLC27L4ACN	TLC27L9ID	TLC27M4AIN
TLC279CN	TLC27L4AID	TLC27L9IN	TLC27M4BCD
TLC279ID	TLC27L4AIN	TLC27L9MD	TLC27M4BCN
TLC279IN	TLC27L4BCD	TLC27L9MFK	TLC27M4BID

Multisim 14.1 Education Components

TLC27M4BIN	TLC339CD	TLC3702MFK	TLC374ID
TLC27M4CD	TLC339CN	TLC3702MJG	TLC374IN
TLC27M4CN	TLC339ID	TLC3702QJG	TLC374MD
TLC27M4ID	TLC339IN	TLC3704CD	TLC374MFK
TLC27M4IN	TLC339MD	TLC3704CN	TLC374MJ
TLC27M4MD	TLC339MN	TLC3704CPW	TLC374MN
TLC27M4MFK	TLC339QD	TLC3704ID	TLC374QD
TLC27M4MJ	TLC339QN	TLC3704IN	TLC374QN
TLC27M4MN	TLC352CD	TLC3704MFK	TLC393CD
TLC27M7CD	TLC352CP	TLC3704MJ	TLC393CP
TLC27M7CP	TLC352ID	TLC3704QJ	TLC393ID
TLC27M7ID	TLC352IP	TLC372CD	TLC393IP
TLC27M7IP	TLC352MFK	TLC372CP	TLC393MD
TLC27M7MD	TLC352MJG	TLC372CPW	TLC393MFK
TLC27M7MFK	TLC354CD	TLC372ID	TLC393MJG
TLC27M7MJG	TLC354CN	TLC372IP	TLC393MP
TLC27M7MP	TLC354CPW	TLC372MD	TLC551CD
TLC27M9CD	TLC354ID	TLC372MFK	TLC551CP
TLC27M9CN	TLC354IN	TLC372MJG	TLC552C
TLC27M9ID	TLC354MD	TLC372MP	TLC552CD
TLC27M9IN	TLC354MN	TLC372QD	TLC552CN
TLC27M9MD	TLC3702CD	TLC372QP	TLC555CD
TLC27M9MFK	TLC3702CP	TLC374CD	TLC555CP
TLC27M9MJ	TLC3702ID	TLC374CN	TLC555CPSR
TLC27M9MN	TLC3702IP	TLC374CPW	TLC555CPW

Multisim 14.1 Education Components

TLC555ID	TLE2021MJG	TLE2024AMN	TLE2027AMP
TLC555IP	TLE2021MP	TLE2024BCDW	TLE2027CD
TLC555QDR	TLE2021Y	TLE2024BCN	TLE2027CP
TLC556CD	TLE2022ACD	TLE2024BIDW	TLE2027ID
TLC556CN	TLE2022ACP	TLE2024BIN	TLE2027IP
TLC556ID	TLE2022AID	TLE2024BMDW	TLE2027MD
TLC556IN	TLE2022AIP	TLE2024BMJ	TLE2027MFK
TLE2021ACD	TLE2022BCD	TLE2024BMN	TLE2027MJG
TLE2021ACP	TLE2022BCP	TLE2024CDW	TLE2027ML
TLE2021AID	TLE2022BID	TLE2024CN	TLE2027MP
TLE2021AIP	TLE2022BIP	TLE2024IDW	TLE2037ACD
TLE2021AMD	TLE2022CD	TLE2024IN	TLE2037ACP
TLE2021AMFK	TLE2022CDBLE	TLE2024MDW	TLE2037AID
TLE2021AMJG	TLE2022CP	TLE2024MFK	TLE2037AIP
TLE2021AMP	TLE2022CPWLE	TLE2024MJ	TLE2037AMD
TLE2021BI	TLE2022ID	TLE2024MN	TLE2037AMFK
TLE2021BMJG	TLE2022IP	TLE2024Y	TLE2037AMJG
TLE2021CD	TLE2022Y	TLE2027ACD	TLE2037AML
TLE2021CDBLE	TLE2024ACDW	TLE2027ACP	TLE2037AMP
TLE2021CP	TLE2024ACN	TLE2027AID	TLE2037CD
TLE2021CPWLE	TLE2024AIDW	TLE2027AIP	TLE2037CP
TLE2021ID	TLE2024AIN	TLE2027AMD	TLE2037ID
TLE2021IP	TLE2024AMDW	TLE2027AMFK	TLE2037IP
TLE2021MD	TLE2024AMFK	TLE2027AMJG	TLE2037MD
TLE2021MFK	TLE2024AMJ	TLE2027AML	TLE2037MFK

Multisim 14.1 Education Components

TLE2037MJG	TLE2061ID	TLE2062CD	TLE2064MD
TLE2037ML	TLE2061IL	TLE2062CP	TLE2064MFK
TLE2037MP	TLE2061IP	TLE2062ID	TLE2064MJ
TLE2061ACD	TLE2061MD	TLE2062IP	TLE2064MN
TLE2061ACL	TLE2061MFK	TLE2062MD	TLE2064Y
TLE2061ACP	TLE2061MJG	TLE2062MFK	TLE2071CD
TLE2061AID	TLE2061ML	TLE2062MJG	TLE2071CP
TLE2061AIL	TLE2061MP	TLE2062MP	TLE2071MFK
TLE2061AIP	TLE2061Y	TLE2062Y	TLE2071MJG
TLE2061AMD	TLE2062ACD	TLE2064ACD	TLE2072CD
TLE2061AMFK	TLE2062ACP	TLE2064ACN	TLE2072CP
TLE2061AMJG	TLE2062AID	TLE2064AID	TLE2072MFK
TLE2061AML	TLE2062AIP	TLE2064AIN	TLE2074CN
TLE2061AMP	TLE2062AMD	TLE2064AMD	TLE2081CD
TLE2061BCL	TLE2062AMFK	TLE2064AMFK	TLE2081CP
TLE2061BIL	TLE2062AMJG	TLE2064AMJ	TLE2081MFK
TLE2061BIP	TLE2062AMP	TLE2064AMN	TLE2081MJG
TLE2061BMJG	TLE2062BCD	TLE2064BCN	TLE2082ACD
TLE2061BML	TLE2062BCP	TLE2064BIN	TLE2082ACP
TLE2061BMP	TLE2062BID	TLE2064BMJ	TLE2082AID
TLE2061CD	TLE2062BIP	TLE2064BMN	TLE2082AIP
TLE2061CDBLE	TLE2062BMD	TLE2064CD	TLE2082AMD
TLE2061CL	TLE2062BMFK	TLE2064CN	TLE2082AMFK
TLE2061CP	TLE2062BMJG	TLE2064ID	TLE2082AMJG
TLE2061CPWLE	TLE2062BMP	TLE2064IN	TLE2082AMP

Multisim 14.1 Education Components

TLE2082CD	TLE2141Y	TLE2144IDW	TLE2161MD
TLE2082CP	TLE2142ACD	TLE2144IN	TLE2161MFK
TLE2082ID	TLE2142ACP	TLE2144MDW	TLE2161MJG
TLE2082IP	TLE2142AID	TLE2144MFK	TLE2161ML
TLE2082MD	TLE2142AIP	TLE2144MJ	TLE2161MP
TLE2082MFK	TLE2142AMD	TLE2144MN	TLE2227ACP
TLE2082MJG	TLE2142AMFK	TLE2144Y	TLE2227CDW
TLE2082MP	TLE2142AMJG	TLE2161ACD	TLE2227CP
TLE2084CN	TLE2142AMP	TLE2161ACP	TLE2237ACP
TLE2141ACD	TLE2142CD	TLE2161AID	TLE2237CDW
TLE2141ACP	TLE2142CP	TLE2161AIP	TLE2237CP
TLE2141AID	TLE2142ID	TLE2161AMD	TLE2425CD
TLE2141AIP	TLE2142IP	TLE2161AMFK	TLE2425ID
TLE2141AMD	TLE2142MD	TLE2161AMJG	TLE2426CD
TLE2141AMFK	TLE2142MFK	TLE2161AML	TLE2426IP
TLE2141AMJG	TLE2142MJG	TLE2161AMP	TL-OP
TLE2141AMP	TLE2142MP	TLE2161BCP	TL-OP1
TLE2141CD	TLE2142Y	TLE2161BIP	TLV1701AIDBVT
TLE2141CP	TLE2144ACN	TLE2161BMJ	TLV1701AIDCKT
TLE2141ID	TLE2144AIN	TLE2161BML	TLV1701AIDRLT
TLE2141IP	TLE2144AMFK	TLE2161BMP	TLV171IDBVT
TLE2141MD	TLE2144AMJ	TLE2161CD	TLV171IDR
TLE2141MFK	TLE2144AMN	TLE2161CP	TLV2211CDBV
TLE2141MJG	TLE2144CDW	TLE2161ID	TLV2211IDBV
TLE2141MP	TLE2144CN	TLE2161IP	TLV2221CDBV

Multisim 14.1 Education Components

TLV2221IDBV	TLV2264MJ	TLV2352IPW	TLV2374IN
TLV2231CDBV	TLV2264QD	TLV2354ID	TLV2374IPW
TLV2231IDBV	TLV2322ID	TLV2354IN	TLV2375ID
TLV2252ID	TLV2322IP	TLV2354IPW	TLV2375IN
TLV2252IP	TLV2322IPWLE	TLV2354MJ	TLV2375IPW
TLV2252MFK	TLV2324ID	TLV2361CDBV	TLV2401CD
TLV2252MJG	TLV2324IN	TLV2361IDBV	TLV2401CDBV
TLV2252MU	TLV2324IPWLE	TLV2362ID	TLV2401ID
TLV2254AID	TLV2332ID	TLV2362IDGK	TLV2401IDBV
TLV2254AIN	TLV2332IP	TLV2362IP	TLV2401IP
TLV2254AIPWLE	TLV2332IPWLE	TLV2362IPS	TLV2402CD
TLV2254ID	TLV2334ID	TLV2362IPW	TLV2402CDGK
TLV2254IN	TLV2334IN	TLV2370ID	TLV2402ID
TLV2254MFK	TLV2334IPWLE	TLV2370IDBV	TLV2402IDGK
TLV2254MJ	TLV2341ID	TLV2370IP	TLV2402IP
TLV2254QD	TLV2341IP	TLV2371ID	TLV2432AID
TLV2262AIPWLE	TLV2341IPWLE	TLV2371IDBV	TLV2432AIPW
TLV2262ID	TLV2342ID	TLV2371IP	TLV2432AMJG
TLV2262IP	TLV2342IP	TLV2372ID	TLV2434AID
TLV2262MFK	TLV2342IPWLE	TLV2372IDGK	TLV2434AIPW
TLV2262MJG	TLV2344ID	TLV2372IP	TLV2442CD
TLV2262MU	TLV2344IN	TLV2373ID	TLV2442CPW
TLV2264AIPWLE	TLV2344IPWLE	TLV2373IDGS	TLV2442MJG
TLV2264ID	TLV2352ID	TLV2373IN	TLV2444CD
TLV2264IN	TLV2352IP	TLV2374ID	TLV2444CPW

Multisim 14.1 Education Components

TLV2444ID	TLV2471AIP	TLV274IPW	TLV2784AIPW
TLV2444IPW	TLV2472AID	TLV2760ID	TLV2785AID
TLV2450AID	TLV2472AIP	TLV2760IDBV	TLV2785AIPW
TLV2450AIP	TLV2473AID	TLV2760IP	TLV3012AIDBVR
TLV2451AID	TLV2473AIP	TLV2761ID	TLV3012AIDCKR
TLV2451AIP	TLV2474AID	TLV2761IDBV	TLV313IDBVT
TLV2452AID	TLV2474AIN	TLV2761IP	TLV313IDCKT
TLV2452AIP	TLV2474AIPWP	TLV2762ID	TLV314IDBVT
TLV2453AID	TLV2475AID	TLV2762IDGK	TLV314IDCKT
TLV2453AIN	TLV2475AIN	TLV2762IP	TLV316IDBVT
TLV2454AID	TLV2475AIPWP	TLV2763ID	TLV316IDCKT
TLV2454AIN	TLV271CD	TLV2763IDGS	TLV3201AIDBVR
TLV2454AIPW	TLV271CDBVR	TLV2763IN	TLV3201AIDCKR
TLV2455AID	TLV271ID	TLV2764ID	TLV3202AID
TLV2455AIN	TLV271IDBVR	TLV2764IN	TLV3202AIDGK
TLV2455AIPW	TLV271IP	TLV2764IPW	TLV333IDBVT
TLV2460CD	TLV272CD	TLV2765ID	TLV333IDCKT
TLV2460CDBV	TLV272CDGK	TLV2765IN	TLV333IDR
TLV2460CP	TLV272ID	TLV2765IPW	TLV3401CD
TLV2461CD	TLV272IDGK	TLV2772CD	TLV3401CDBVR
TLV2461CDBV	TLV272IP	TLV2772CDGK	TLV3401ID
TLV2461CP	TLV274CD	TLV2772CP	TLV3401IDBVR
TLV2470AID	TLV274CPW	TLV2782AID	TLV3401IDG4
TLV2470AIP	TLV274ID	TLV2783AID	TLV3401IP
TLV2471AID	TLV274IN	TLV2784AID	TLV342ID

Multisim 14.1 Education Components

TLV342IDGKR	TLV4112ID	TLV7111830DSER	TLVH431ILPR
TLV342IRUGR	TLV4112IDGN	TLV73310PDBVR	TLVH431IPK
TLV3492AID	TLV4112IP	TLV73310PDQNR	TLVH431QDBVR
TLV3492AIDCNT	TLV4113CDGQR	TLV73311PDBVR	TLVH431QDBZR
TLV3494AID	TLV4113ID	TLV73311PDQNR	TLVH431QDCKR
TLV3494AIPWT	TLV4113IDGQ	TLV73312PDBVR	TLVH431QLP
TLV3501AID	TLV4113IN	TLV73312PDQNR	TLVH431QLPR
TLV3501AIDBVR	TLV431CDBVR	TLV73315PDBVR	TLVH431QPK
TLV3691IDCKR	TLV431CDBZR	TLV73315PDQNR	TMP20AIDCKR
TLV3691IDPFR	TLV431CLP	TLV73318PDBVR	TMP20AIDRLR
TLV3701CD	TLV431CLPM	TLV73318PDQNR	TN2219
TLV3701CDBVR	TLV431CLPR	TLV73325PDBVR	TN2219A
TLV3701ID	TLV431IDBVR	TLV73325PDQNR	TN2905
TLV3701IDBVR	TLV431IDBZR	TLV73333PDBVR	TN2905A
TLV3701IP	TLV431ILP	TLV73333PDQNR	TN4036
TLV4110ID	TLV431ILPR	TLVH431CDBVR	TOSHIBA-MIPS-HDR
TLV4110IDGNR	TLV431QPK	TLVH431CDBZR	TP0610K-T1-GE3
TLV4110IP	TLV521DCKT	TLVH431CDCKR	TPA301D
TLV4111CD	TLV522DGKT	TLVH431CLP	TPA301DGN
TLV4111CDGN	TLV6001IDBVT	TLVH431CLPR	TPA301DR
TLV4111ID	TLV6001IDCKT	TLVH431CPK	TPS3780ADBVR
TLV4111IDGN	TLV70213DBVT	TLVH431IDBVR	TPS3780BDBVR
TLV4112CD	TLV70711PDQNR	TLVH431IDBZR	TPS3780CDBVR
TLV4112CDGN	TLV70717DQNR	TLVH431IDCKR	TPS3780DDBVR
TLV4112CP	TLV707335DQNR	TLVH431ILP	TPS3803-01DCKR

Multisim 14.1 Education Components

TPS3839G25DBZR	TPS71711DCKR	TPS72728DSET	TPS76725QD
TPS70612DBVR	TPS71712DCKR	TPS72728YFFT	TPS76725QPWP
TPS70612DRVR	TPS71713DCKR	TPS73530QDRBRQ1	TPS76727QD
TPS70615DBVR	TPS71715DCKR	TPS73601DBVT	TPS76727QPWP
TPS70615DRVR	TPS71719DCKR	TPS73601DCQ	TPS76728QD
TPS70618DBVR	TPS71721DCKR	TPS73601DRBT	TPS76730QD
TPS70618DRVR	TPS71726DCKR	TPS75701KC	TPS76730QPWP
TPS70625DBVR	TPS71727DCKR	TPS75701KTTT	TPS76733QD
TPS70625DRVR	TPS71727DSER	TPS76150DBVR	TPS76733QPWP
TPS70628DBVR	TPS717285DCKR	TPS76301DBVR	TPS76750QD
TPS70628DRVR	TPS71729DCKR	TPS76316DBVR	TPS76750QPWP
TPS70630DBVR	TPS71730DCKR	TPS76318DBVR	TPS76801QD
TPS70630DRVR	TPS71733DCKR	TPS76325DBVR	TPS76801QPWP
TPS70633DBVR	TPS71733DRVR	TPS76327DBVR	TPS76815QD
TPS70633DRVR	TPS71733DSER	TPS76328DBVR	TPS76815QPWP
TPS70925DBVR	TPS71750DSER	TPS76330DBVR	TPS76818QD
TPS70925DRVR	TPS72711YFFR	TPS76333DBVR	TPS76818QPWP
TPS70950DBVR	TPS72715DSET	TPS76338DBVR	TPS76825QD
TPS70950DRVR	TPS72715YFFT	TPS76350DBVR	TPS76825QPWP
TPS715A33DRBT	TPS727185YFFR	TPS76701QD	TPS76827QD
TPS715A33DRVT	TPS72718DSET	TPS76701QPWPR	TPS76828QD
TPS71701DCKR	TPS72718YFFT	TPS76715QD	TPS76830QD
TPS71709DSER	TPS72725DSET	TPS76715QPWP	TPS76830QPWP
TPS71710DCKR	TPS72727DSET	TPS76718QD	TPS76833QD
TPS71710DRVR	TPS727285DSER	TPS76718QPWP	TPS76833QPWP

Multisim 14.1 Education Components

TPS76850QD	TPS7A4901DGNR	TPSMP24AHM3/84 A	TRIANGULAR_CURR ENT
TPS76850QPWP	TPS7A4901DRBR		
TPS77618QPWPRQ 1	TPS7A7300RGWR	TPSMP27AHE3/84A	TRIANGULAR_VOLT AGE
TPS780230300DRV R	TPS7A8300RGRR	TPSMP30AHM3/84 A	TRIODE_VIRTUAL
TPS78618DCQR	TPS7A8300RGWR	TPSMP36AHM3/84 A	TRISTATE
TPS78618KTTT	TPSMA16AHE3/61T		TRISTATE_NEG
TPS78625DCQR	TPSMA20A/11T	TRAFFIC_LIGHT	TS_VIRTUAL
TPS78625KTTT	TPSMA27AHE3/61T	TRAFFIC_LIGHT_SIN GLE	TS5A3357DCUR
TPS78628DCQR	TPSMA30AHE3/61T	TRANSFER_FUNCTI ON_BLOCK	TS5A3359DCUR
TPS78628KTTT	TPSMA33AHE3/61T		TS5A3359YZPR
TPS78630DCQR	TPSMA36AHE3/5AT	TRANSFORMER_CT _RATED	TVS3V3L4U
TPS78630KTTT	TPSMB24AHE3/52T	TRANSFORMER_RA TED	U257
TPS78633DCQR	TPSMB27A/2		U308
TPS78633KTTT	TPSMB30AHE3/52T	TRANSISTOR	U309
TPS79301DBVR	TPSMB33AHE3/52T	TRANSISTOR_DELA Y	U310
TPS79516DCQR	TPSMB36A/5T		U401
TPS79518DCQR	TPSMB39A-E3/2T	TRANSISTOR_DIOD E	U402
TPS79525DCQR	TPSMC22A-E3/57T	TRANSISTOR_DIOD E_DELAY	U403
TPS79533DCQR	TPSMC27A-E3/57T		U404
TPS79718DCKR	TPSMC30AHE3_A/H	TRANSPORT_DELAY	U405
TPS797285DCKR	TPSMC33A-E3/51T	TRF37A75IDSGR	U406
TPS79730DCKR	TPSMC36A/9AT	TRF37B75IDSGR	U440
TPS79733DCKR	TPSMC39A-E3/57T	TRF37C75IDSGR	U441
TPS799L54YZYR	TPSMP18AHM3/84 A	TRIAC	UA709AMJ UA709AMJG

Multisim 14.1 Education Components

UA709AMU	UA748CP	UCC37321D	V_REF4
UA709AMW	UA748JG	UCC37321DGN	V_REF5
UA709CD	UA748MJG	UCC37321P	V10P10-M3/86A
UA709CJG	UA748MU	UCC37322D	V12P10-M3/86A
UA709CP	UC1705	UCC37322DGN	V8P10HM3/86A
UA709MJ	UC2715D	UCC37322P	VARIABLE_CAPACIT OR
UA709MU	UC2715DP	UF4002-E3/54	VARIABLE_CAPACIT OR_RATED
UA709MW	UC3248	UF4007-E3/54	VARIABLE_CAPACIT OR_VIRTUAL
UA723CD	UC3715D	UF5406-E3/54	VARIABLE_CAPACIT OR_VIRTUAL
UA723CFK	UC3842	UG06D-E3/54	VARIABLE_INDUCT OR
UA723CJ	UCC27321D	UG1D-E3/54	VARIABLE_INDUCT OR_RATED
UA723CN	UCC27321DGN	UG30DPT-E3/45	VARIABLE_INDUCT OR_VIRTUAL
UA723MU	UCC27321P	UG5JT-E3/45	VARIABLE_PULLUP_ VIRTUAL
UA741CD	UCC27322D	UG8DT-E3/45	VARIABLE_RESISTO R_VIRTUAL
UA741CP	UCC27322DGN	UG8JCT-E3/45	VARICAP
UA741MFK	UCC27322P	UG8JTHE3/45	VARICOIL
UA741MJ	UCC27423D	UNDCD_BARGRAPH	VARIRES
UA741MJG	UCC27423DGN	US1G-E3/61T	VBP104FAS
UA741MU	UCC27423P	US1J-E3/5AT	VBP104FASR
UA747CD	UCC27424D	US1M-E3/61T	VBPW34FAS
UA747CN	UCC27424DGN	UVLO	VBPW34FASR
UA747MFK	UCC27424P	UX60-MB-5ST	
UA747MJ	UCC27425D	V_REF1	
UA747MW	UCC27425DGN	V_REF2	
UA748CD	UCC27425P	V_REF3	

Multisim 14.1 Education Components

VBPW34S	VO2601	VO615A-3X009T	VOLTAGE_CONTROLLED_SPST_ANIMATED
VBPW34SR	VO2601-X006	VO615A-3X016	
VCA810AID	VO2601-X007T	VO615A-3X017T	VOLTAGE_CONTROLLED_SPST_BOUNCE
VCA810ID	VO2601-X016	VO615A-3X018T	
VCA821ID	VO2601-X017T	VO615A-3X019T	VOLTAGE_CONTROLLED_SQUARE_WAVE
VCA824ID	VO2611	VOLTAGE_CONTROLLED_CAPACITOR_VIRTUAL	
VCA8500IRGCR	VO2611-X006		VOLTAGE_CONTROLLED_TRIANGLE_WAVE
VCC	VO2611-X007T	VOLTAGE_CONTROLLED_CURRENT_SOURCE	
VDAC	VO2611-X016		VOLTAGE_CONTROLLED_VOLTAGE_SOURCE
VDAC16	VO2611-X017T	VOLTAGE_CONTROLLED_DPDT	
VDD	VO2630		VOLTAGE_DIFFERENTIATOR
VEC2315-TL-H	VO2630-X006	VOLTAGE_CONTROLLED_INDUCTOR_VIRTUAL	
VEC2315-TL-W	VO2630-X007T		VOLTAGE_GAIN_BLOCK
VEC2616-TL-H	VO2631	VOLTAGE_CONTROLLED_LIMITER	
VEC2616-TL-W	VO2631-X006		VOLTAGE_HYSTeresis_BLOCK
VEE	VO2631-X007T	VOLTAGE_CONTROLLED_PIECEWISE_LINEAR_SOURCE	
VN10LF	VO2631-X017T		VOLTAGE_INTEGRATOR
VO0600T	VO4661	VOLTAGE_CONTROLLED_RESISTOR_VIRTUAL	VOLTAGE_LIMITER
VO0601T	VO4661-X006		VOLTAGE_SLEW_RATE_BLOCK
VO0601-X001T	VO4661-X007T	VOLTAGE_CONTROLLED_SINE_WAVE	
VO0611T	VO615A-3		VOLTAGE_SUMMER
VO0630T	VO615A-3X001	VOLTAGE_CONTROLLED_SPDT	VOLTAGE_TRIGGERED_PIECEWISE_LINEAR_SOURCE
VO0631T	VO615A-3X006		
VO0631-X001T	VO615A-3X007T	VOLTAGE_CONTROLLED_SPST	VOLTMETER_H
VO0661T	VO615A-3X008T		VOLTMETER_HR

Multisim 14.1 Education Components

VOLTMETER_V	XNOR6	Z_LOAD2_DELTA	ZC820
VOLTMETER_VR	XNOR6	Z_LOAD2_WYE	ZC821
VOM452T	XNOR7	Z_LOAD3	ZC822
VOM453T	XNOR7	Z4KE100	ZC823
VSKY20301608-G4-08	XNOR8	Z4KE100A	ZC824
	XNOR8	Z4KE110	ZC825
VSKY20401608-G4-08	XOR2	Z4KE110A	ZC826
	XOR2	Z4KE120	ZC830A
VSS	XOR3	Z4KE120A	ZC831A
W06G-E4/51	XOR3	Z4KE130	ZC832A
	XOR4	Z4KE130A	ZC833A
WE300B	XOR4	Z4KE140	ZC834A
WOBBLE_STICK	XOR5	Z4KE140A	ZC835A
	XOR5	Z4KE150	ZC836A
XILINX-PARALLEL-III-IV-HDR	XOR6	Z4KE150A	ZDX1F
	XOR6	Z4KE160	ZDX2F
XILINX-PARALLEL-IV-HDR	XOR7	Z4KE160A	ZDX5
	XOR7	Z4KE170	ZENER
XNOR2	XOR8	Z4KE170A	ZGL41_100
XNOR2	XOR8	Z4KE180	ZGL41_110
XNOR3	XTR300AIRGWR	Z4KE180A	ZGL41_120
XNOR3		Z_LOAD1	ZGL41_130
XNOR4	Z_LOAD1_DELTA	Z4KE190	ZGL41_140
XNOR4	Z_LOAD1_WYE	Z4KE190A	ZGL41_150
XNOR5	Z_LOAD2	Z4KE200	ZGL41_160
XNOR5		Z4KE200A	

Multisim 14.1 Education Components

ZGL41_170	ZPD4.7	ZTX214	ZTX614
ZGL41_180	ZPD5.1	ZTX214A	ZTX618
ZGL41_190	ZPD6.2	ZTX237	ZTX649
ZGL41_200	ZPD6.8	ZTX237B	ZTX650
ZHCS1000	ZPD7.5	ZTX238	ZTX651
ZHCS750	ZPD8.2	ZTX238B	ZTX653
ZPD10	ZTX1047A	ZTX239	ZTX657
ZPD11	ZTX1048A	ZTX239B	ZTX658
ZPD12	ZTX1049A	ZTX320	ZTX688B
ZPD13	ZTX1051A	ZTX321	ZTX689B
ZPD15	ZTX1053A	ZTX325	ZTX690B
ZPD16	ZTX1055A	ZTX327	ZTX692B
ZPD18	ZTX107	ZTX337A	ZTX694B
ZPD2.7	ZTX107B	ZTX338A	ZTX696B
ZPD20	ZTX108	ZTX360	ZTX704
ZPD22	ZTX108B	ZTX450	ZTX705
ZPD24	ZTX109	ZTX454	ZTX718
ZPD27	ZTX109B	ZTX455	ZTX749
ZPD3.0	ZTX1147A	ZTX458	ZTX750
ZPD3.3	ZTX1149A	ZTX549	ZTX751
ZPD3.6	ZTX1151A	ZTX550	ZTX753
ZPD3.9	ZTX212	ZTX558	ZTX757
ZPD30	ZTX212A	ZTX601B	ZTX758
ZPD33	ZTX213	ZTX604	ZTX788A
ZPD4.3	ZTX213A	ZTX605	ZTX788B

Multisim 14.1 Education Components

ZTX789A	ZVN4306G
ZTX790A	ZVN4310G
ZTX792A	ZVN4424G
ZTX795A	ZVP2106A
ZTX796A	ZVP2106G
ZTX849	ZVP3306
ZTX851	ZVP3306F
ZTX857	ZVP4424A
ZTX869	ZVP4424G
ZTX948	
ZTX949	
ZTX951	
ZTX953	
ZTX955	
ZTX956	
ZTX957	
ZTX958	
ZTX968	
ZVN0124A	
ZVN2106A	
ZVN2106G	
ZVN3306A	
ZVN3306F	
ZVN3310F	
ZVN4210G	