

# Multisim 14.0 Education Components

---

741	1787386	1 mF [T510X108M004AT	1 mF [T520Y108M2R5AT
1028	1787580	E018]	E015]
1294	685119136923	1 mF	1 mF
2462	0.5_AMP	[T510X108M004AT	[T520Y108M2R5AT
2466	02BZ2.2	E023]	E025]
2468	02DZ4.7	1 mF	1 mF
2477	05AZ2.2	[T513E108M004AH	[T530X108M003AT
2481	1 mF	6110]	E010]
8051	[T491E108M004AT]	1 mF	1 mF
8052	1 mF	[T513X108M004AH	[T530X108M004AT
284258	[T491X108M004AT]	6110]	E006]
1708026	1 mF	1 mF	1 mF
1708039	[T494E108M004AT]	[T513X108M004AH	[T530X108M2R5AT
1708042	1 mF	6120]	E005]
1708055	[T494X108M004AT]	1 mF	1 mF
1708084	1 mF	[T520D108M2R5AT	[T530X108M2R5AT
1708110	[T495E108M004AT	E015]	E006]
1786837	E035]	1 mF	1 mF
1786866	1 mF	[T520D108M2R5AT	[T530Y108M2R5AT
1786918	[T495X108M004AT	E030]	E005]
1786963	E070]	1 mF	1 nF
1787205	1 mF	[T520X108M003AT	[C0402C102K1HACT
1787234	[T510E108M004AT	E015]	U]
1787289	E010]	1 mF	1 nF
1787331	1 mF	[T520X108M003AT	[C0402C102K3GACT
	[T510E108M004AT	E030]	U]
	E018]	1 mF	1 nF
		[T520X108M2R5AT	[C0402C102K3HACT
		E010]	U]
		1 mF	1 nF
		[T520Y108M2R5AT	[C0402C102K3RACT
		E010]	U]

# Multisim 14.0 Education Components

---

1 nF [C0402C102K4RACT U]	1 nF [C0603C102K4GACT U]	1 nF [C0805C102K3RACT U]	1 nF [C1206C102K4RACT U]
1 nF [C0402C102K5HACT U]	1 nF [C0603C102K4RACT U]	1 nF [C0805C102K4RACT U]	1 nF [C1206C102K5GACT U]
1 nF [C0402C102K5RACT U]	1 nF [C0603C102K5GACT U]	1 nF [C0805C102K5GACT U]	1 nF [C1206C102K5RACT U]
1 nF [C0402C102K8RACT U]	1 nF [C0603C102K5HACT U]	1 nF [C0805C102K5RACT U]	1 nF [C1206C102KCGAC TU]
1 nF [C0402C102K9RACT U]	1 nF [C0603C102K5RACT U]	1 nF [C0805C102K8RACT U]	1 nF [C1210C102K1GACT U]
1 nF [C0603C102K1HACT U]	1 nF [C0603C102K8RACT U]	1 nF [C0805C102KARACT U]	1 nF [C1210C102K2GACT U]
1 nF [C0603C102K1RACT U]	1 nF [C0603C102K9RACT U]	1 nF [C1206C102K1GACT U]	1 nF [C1210C102K5GACT U]
1 nF [C0603C102K2RACT U]	1 nF [C0805C102K1GACT U]	1 nF [C1206C102K1RACT U]	1 nF [C1210C102KBGAC TU]
1 nF [C0603C102K3GACT U]	1 nF [C0805C102K1RACT U]	1 nF [C1206C102K2GACT U]	1 nF [C1210C102KCGAC TU]
1 nF [C0603C102K3HACT U]	1 nF [C0805C102K2RACT U]	1 nF [C1206C102K2RACT U]	1 nF [C1210C102KDGAC TU]
1 nF [C0603C102K3RACT U]	1 nF [C0805C102K3GACT U]	1 nF [C1206C102K3RACT U]	1 nF [C1812C102K1GACT U]

# Multisim 14.0 Education Components

---

1 nF [C1812C102K2GACT U]	1 nF [CA064C102K8RACT U]	1 uF [C0805C105K4PACT U]	1 uF [C1206C105K3PACT U]
1 nF [C1812C102K5GACT U]	1 uF [C0402C105K8PACT U]	1 uF [C0805C105K4RACT U]	1 uF [C1206C105K3RACT U]
1 nF [C1812C102KBGAC TU]	1 uF [C0402C105K9PACT U]	1 uF [C0805C105K8NAC TU]	1 uF [C1206C105K4RACT U]
1 nF [C1812C102KCGAC TU]	1 uF [C0603C105K3PACT U]	1 uF [C0805C105K8PACT U]	1 uF [C1206C105K5RACT U]
1 nF [C1812C102KDGAC TU]	1 uF [C0603C105K4PACT U]	1 uF [C0805C105K8RACT U]	1 uF [C1206C105K8RACT U]
1 nF [C1825C102KBGAC TU]	1 uF [C0603C105K4RACT U]	1 uF [C0805C105K9PACT U]	1 uF [C1206C105K9RACT U]
1 nF [C2220C102KBGAC TU]	1 uF [C0603C105K8PACT U]	1 uF [C0805C105K9RACT U]	1 uF [C1206C105M3VAC TU]
1 nF [C2225C102KBGAC TU]	1 uF [C0603C105K8RACT U]	1 uF [C0805C105M3VAC TU]	1 uF [C1206C105M4VAC TU]
1 nF [CA064C102K3RACT U]	1 uF [C0603C105K9PACT U]	1 uF [C0805C105M4VAC TU]	1 uF [C1206C105M8VAC TU]
1 nF [CA064C102K4RACT U]	1 uF [C0603C105K9RACT U]	1 uF [C0805C105M8VAC TU]	1 uF [C1206F105K4RACT U]
1 nF [CA064C102K5RACT U]	1 uF [C0805C105K3PACT U]	1 uF [C1206C105K3NAC TU]	1 uF [C1210C105K1RACT U]

# Multisim 14.0 Education Components

---

1 uF [C1210C105K3PACT U]	1 uF [C1210C105M8VAC TU]	1 uF [C1825C105KARACT U]	1 uF [T491A105M016AT]
1 uF [C1210C105K3RACT U]	1 uF [C1210F105K3RACT U]	1 uF [C1825C105M5UAC TU]	1 uF [T491A105M020AT]
1 uF [C1210C105K4PACT U]	1 uF [C1210F105K4RACT U]	1 uF [C2220C105K5R1C7 186]	1 uF [T491A105M025AT]
1 uF [C1210C105K4RACT U]	1 uF [C1812C105K3RACT U]	1 uF [C2220C105K5RACT U]	1 uF [T491B105M025AT]
1 uF [C1210C105K5NAC TU]	1 uF [C1812C105K5RACT U]	1 uF [C2220C105KARACT U]	1 uF [T491B105M035AT]
1 uF [C1210C105K5PACT U]	1 uF [C1812C105M5UAC TU]	1 uF [C2225C105K1RACT U]	1 uF [T491C105M050AT]
1 uF [C1210C105K5RACT U]	1 uF [C1812F105K1RACT U]	1 uF [C2225C105K5RACT U]	1 uF [T491S105M020AT]
1 uF [C1210C105K8RACT U]	1 uF [C1812F105K3RACT U]	1 uF [C2225C105KARACT U]	1 uF [T491V105M050AT]
1 uF [C1210C105K9RACT U]	1 uF [C1812F105K5RACT U]	1 uF [C2225C105M5UAC TU]	1 uF [T494A105M016AT]
1 uF [C1210C105M3VAC TU]	1 uF [C1825C105K2RACT U]	1 uF [T409C105M025AH 4250]	1 uF [T494A105M020AT]
1 uF [C1210C105M5UAC TU]	1 uF [C1825C105K5RACT U]	1 uF [T489A105M025AT E6K6]	1 uF [T494A105M025AT]
			1 uF [T494A105M035AT]
			1 uF [T494B105M025AT]

# Multisim 14.0 Education Components

---

1 uF [T494B105M035AT]	1.1 nF [C0402C112K3HACT U]	1.2 nF [C0402C122K3HACT U]	1.2 nF [C0603C122K5RACT U]
1 uF [T494B105M050AT]	1.1 nF [C0402C112K5HACT U]	1.2 nF [C0402C122K3RACT U]	1.2 nF [C0805C122K1GACT U]
1 uF [T494C105M050AT]	1.1 nF [C0603C112K1HACT U]	1.2 nF [C0402C122K4RACT U]	1.2 nF [C0805C122K1RACT U]
1 uF [T494V105M050AT]	1.1 nF [C0603C112K3HACT U]	1.2 nF [C0402C122K5HACT U]	1.2 nF [C0805C122K2RACT U]
1 uF [T495A105M020AT E3K0]	1.1 nF [C0603C112K5HACT U]	1.2 nF [C0402C122K5RACT U]	1.2 nF [C0805C122K3GACT U]
1 uF [T495A105M035AT E3K0]	1.1 nF [C1210C112KBGAC TU]	1.2 nF [C0603C122K1HACT U]	1.2 nF [C0805C122K4RACT U]
1 uF [T495B105M035AT E1K7]	1.1 nF [C1812C112KBGAC TU]	1.2 nF [C0603C122K1RACT U]	1.2 nF [C0805C122K5GACT U]
1 uF [T497A105M015AT 6110]	1.1 nF [C1825C112KBGAC TU]	1.2 nF [C0603C122K3HACT U]	1.2 nF [C0805C122K5RACT U]
1 uF [T498A105M016AT E6K5]	1.1 nF [C2220C112KBGAC TU]	1.2 nF [C0603C122K3RACT U]	1.2 nF [C0805C122KARACT U]
1 uF [T498A105M020AT E5K9]	1.1 nF [C2225C112KBGAC TU]	1.2 nF [C0603C122K4RACT U]	1.2 nF [C1206C122K1GACT U]
1 uF [T498A105M035AT E10K]	1.1 nF [CDR33BP112BKSM ]	1.2 nF [C0603C122K5HACT U]	1.2 nF [C1206C122K1RACT U]

# Multisim 14.0 Education Components

---

1.2 nF [C1206C122K2GACT U]	1.2 uF [C0805C125K8PACT U]	1.2 uF [C1825C125M5UAC TU]	1.3 nF [C2220C132KBGAC TU]
1.2 nF [C1206C122K2RACT U]	1.2 uF [C0805C125K8RACT U]	1.2 uF [C2220C125K5RACT U]	1.3 nF [C2225C132KBGAC TU]
1.2 nF [C1206C122K5GACT U]	1.2 uF [C0805C125K9PACT U]	1.2 uF [C2225C125KARACT U]	1.5 mF [T530X158M003AT E008]
1.2 nF [C1206C122K5RACT U]	1.2 uF [C0805C125K9RACT U]	1.3 nF [C0402C132K3HACT U]	1.5 mF [T530X158M2R5AT E005]
1.2 nF [C1210C122KBGAC TU]	1.2 uF [C1206C125K3RACT U]	1.3 nF [C0402C132K5HACT U]	1.5 nF [C0402C152K3HACT U]
1.2 nF [C1812C122KBGAC TU]	1.2 uF [C1206C125K4RACT U]	1.3 nF [C0603C132K1HACT U]	1.5 nF [C0402C152K3RACT U]
1.2 nF [C1825C122KBGAC TU]	1.2 uF [C1206C125K8RACT U]	1.3 nF [C0603C132K3HACT U]	1.5 nF [C0402C152K4RACT U]
1.2 nF [C2220C122KBGAC TU]	1.2 uF [C1210C125K3PACT U]	1.3 nF [C0603C132K5HACT U]	1.5 nF [C0402C152K5HACT U]
1.2 nF [C2225C122KBGAC TU]	1.2 uF [C1210C125K3RACT U]	1.3 nF [C1210C132KBGAC TU]	1.5 nF [C0402C152K5RACT U]
1.2 uF [C0805C125K4PACT U]	1.2 uF [C1210F125K4RACT U]	1.3 nF [C1812C132KBGAC TU]	1.5 nF [C0402C152K8RACT U]
1.2 uF [C0805C125K4RACT U]	1.2 uF [C1825C125K5RACT U]	1.3 nF [C1825C132KBGAC TU]	1.5 nF [C0603C152K1HACT U]

# Multisim 14.0 Education Components

---

1.5 nF [C0603C152K1RACT U]	1.5 nF [C0805C152K3RACT U]	1.5 nF [C1206C152K5RACT U]	1.5 uF [C0805C155K4RACT U]
1.5 nF [C0603C152K2RACT U]	1.5 nF [C0805C152K4GACT U]	1.5 nF [C1210C152K1GACT U]	1.5 uF [C0805C155K8PACT U]
1.5 nF [C0603C152K3HACT U]	1.5 nF [C0805C152K4RACT U]	1.5 nF [C1210C152K5GACT U]	1.5 uF [C0805C155K8RACT U]
1.5 nF [C0603C152K3RACT U]	1.5 nF [C0805C152K5GACT U]	1.5 nF [C1210C152KBGAC TU]	1.5 uF [C0805C155K9PACT U]
1.5 nF [C0603C152K4RACT U]	1.5 nF [C0805C152K5RACT U]	1.5 nF [C1812C152K2GACT U]	1.5 uF [C0805C155K9RACT U]
1.5 nF [C0603C152K5HACT U]	1.5 nF [C0805C152KARACT U]	1.5 nF [C1812C152KBGAC TU]	1.5 uF [C1206C155K3RACT U]
1.5 nF [C0603C152K5RACT U]	1.5 nF [C1206C152K1GACT U]	1.5 nF [C1825C152KBGAC TU]	1.5 uF [C1206C155K4PACT U]
1.5 nF [C0603C152K8RACT U]	1.5 nF [C1206C152K1RACT U]	1.5 nF [C2220C152KBGAC TU]	1.5 uF [C1206C155K4RACT U]
1.5 nF [C0805C152K1GACT U]	1.5 nF [C1206C152K2GACT U]	1.5 nF [C2225C152KBGAC TU]	1.5 uF [C1206C155K8PACT U]
1.5 nF [C0805C152K1RACT U]	1.5 nF [C1206C152K2RACT U]	1.5 nF [CDR04BP152BKSM ]	1.5 uF [C1206C155K8RACT U]
1.5 nF [C0805C152K2RACT U]	1.5 nF [C1206C152K5GACT U]	1.5 uF [C0805C155K4PACT U]	1.5 uF [C1206C155K9RACT U]

# Multisim 14.0 Education Components

---

1.5 uF [C1210C155K3PACT U]	1.5 uF [T491A155M010AT]	1.5 uF [T494C155M035AT]	1.5KE47A-E3/54
			1.5KE47AG
1.5 uF [C1210C155K3RACT U]	1.5 uF [T491A155M016AT]	1.5 uF [T494C155M050AT]	1.5KE47ARL4G
	1.5 uF [T491A155M020AT]	1.5 uF [T494D155M050AT ]	1.5KE51CA-E3/54
1.5 uF [C1210C155K4RACT U]	1.5 uF [T491A155M025AT]	1.5 uF [T494S155M020AT]	1.5KE75ARL4G
			1.5KE91A-E3/54
1.5 uF [C1210F155K4RACT U]	1.5 uF [T491B155M025AT]	1.5 uF [T498C155M035AT E3K3]	1.5KE91ARL4G
	1.5 uF [T491B155M035AT]		1.5SMC12AT3G
1.5 uF [C1825C155K5RACT U]	1.5 uF [T491C155M035AT]	1.5KE100A-E3/54	1.5SMC13A-E3/57T
		1.5KE100CA-E3/54	1.5SMC15AT3G
1.5 uF [C1825C155M5UAC TU]	1.5 uF [T491C155M050AT]	1.5KE110CA-E3/54	1.5SMC15CA- E3/57T
		1.5KE12A-E3/54	1.5SMC180A- E3/57T
1.5 uF [C2220C155K5RACT U]	1.5 uF [T491D155M050AT ]	1.5KE12CA-E3/54	1.5SMC18AT3G
		1.5KE130CA-E3/54	1.5SMC18CA- E3/57T
1.5 uF [C2225C155K5RACT U]	1.5 uF [T491S155M020AT]	1.5KE160CA-E3/54	1.5SMC20AT3G
	1.5 uF [T494A155M010AT]	1.5KE180A-E3/54	1.5SMC24AT3G
1.5 uF [C2225C155M5UAC TU]	1.5 uF [T494A155M016AT]	1.5KE18A-E3/54	1.5SMC33AT3G
		1.5KE200A-E3/54	1.5SMC39A-E3/57T
1.5 uF [T419A155M015AH 4250]	1.5 uF [T494A155M025AT]	1.5KE200CA-E3/54	1.5SMC39AT3G
		1.5KE20A-E3/51	1.5SMC43AT3G
1.5 uF [T489C155M050AT E1K5]	1.5 uF [T494B155M025AT]	1.5KE36A-E3/54	1.5SMC540A- E3/57T
	1.5 uF [T494B155M035AT]	1.5KE36CA-E3/54	1.5SMC6.8A/57T
		1.5KE39ARL4G	
		1.5KE39CA-E3/54	



# Multisim 14.0 Education Components

---

1.5SMC6.8AT3G	1.6 nF [C2220C162KBGAC TU]	1.8 nF [C0805C182K1RACT U]	1.8 nF [C1210C182K1GACT U]
1.5SMC6.8CA- E3/57T			
1.5SMC62AT3G	1.6 nF [C2225C162KBGAC TU]	1.8 nF [C0805C182K2RACT U]	1.8 nF [C1210C182K2GACT U]
1.5SMC75CA- E3/57T			
1.5SMC91AT3G	1.8 nF [C0402C182K3RACT U]	1.8 nF [C0805C182K4RACT U]	1.8 nF [C1210C182K5GACT U]
1.6 nF [C0603C162K1HACT U]	1.8 nF [C0402C182K5RACT U]	1.8 nF [C0805C182K5GACT U]	1.8 nF [C1210C182KBGAC TU]
1.6 nF [C0603C162K3HACT U]	1.8 nF [C0603C182K1HACT U]	1.8 nF [C0805C182K5RACT U]	1.8 nF [C1812C182KBGAC TU]
1.6 nF [C0603C162K5HACT U]	1.8 nF [C0603C182K1RACT U]	1.8 nF [C0805C182KARACT U]	1.8 nF [C1825C182KBGAC TU]
1.6 nF [C0805C162K4GACT U]	1.8 nF [C0603C182K3HACT U]	1.8 nF [C1206C182K1GACT U]	1.8 nF [C2220C182KBGAC TU]
1.6 nF [C1206C162K5GACT U]	1.8 nF [C0603C182K3RACT U]	1.8 nF [C1206C182K1RACT U]	1.8 nF [C2225C182KBGAC TU]
1.6 nF [C1210C162KBGAC TU]	1.8 nF [C0603C182K5HACT U]	1.8 nF [C1206C182K2GACT U]	1.8 uF [C0805C185K4PACT U]
1.6 nF [C1812C162KBGAC TU]	1.8 nF [C0603C182K5RACT U]	1.8 nF [C1206C182K5GACT U]	1.8 uF [C0805C185K4RACT U]
1.6 nF [C1825C162KBGAC TU]	1.8 nF [C0805C182K1GACT U]	1.8 nF [C1206C182K5RACT U]	1.8 uF [C0805C185K8PACT U]

# Multisim 14.0 Education Components

---

1.8 uF [C0805C185K8RACT U]	1.8 uF [C2225C185K5RACT U]	10 nF [C0603C103K2RACT U]	10 nF [C0805C103K3GACT U]
1.8 uF [C0805C185K9PACT U]	1.8 uF [C2225C185M5UAC TU]	10 nF [C0603C103K3GACT U]	10 nF [C0805C103K3HACT U]
1.8 uF [C0805C185K9RACT U]	1 AMP [C0201C103K4PACT U]	10 nF [C0603C103K3HACT U]	10 nF [C0805C103K3RACT U]
1.8 uF [C1206C185K3PACT U]	10 nF [C0201C103K8PACT U]	10 nF [C0603C103K3RACT U]	10 nF [C0805C103K4RACT U]
1.8 uF [C1206C185K4RACT U]	10 nF [C0201C103K9PACT U]	10 nF [C0603C103K4RACT U]	10 nF [C0805C103K5GACT U]
1.8 uF [C1206C185K8RACT U]	10 nF [C0402C103K3RACT U]	10 nF [C0603C103K5RACT U]	10 nF [C0805C103K5HACT U]
1.8 uF [C1210C185K3PACT U]	10 nF [C0402C103K4RACT U]	10 nF [C0603C103K8RACT U]	10 nF [C0805C103K5RACT U]
1.8 uF [C1210C185K3RACT U]	10 nF [C0402C103K5RACT U]	10 nF [C0603C103K9RACT U]	10 nF [C0805C103K8RACT U]
1.8 uF [C1210F185K4RACT U]	10 nF [C0402C103K8RACT U]	10 nF [C0805C103K1GACT U]	10 nF [C0805C103KARACT U]
1.8 uF [C1825C185K5RACT U]	10 nF [C0402C103K9RACT U]	10 nF [C0805C103K1HACT U]	10 nF [C0805C103M1UAC TU]
1.8 uF [C2220C185K5RACT U]	10 nF [C0603C103K1RACT U]	10 nF [C0805C103K1RACT U]	10 nF [C0805C103M5UAC TU]

# Multisim 14.0 Education Components

---

10 nF [C0805F103K1RACT U]	10 nF [C1206C103K4GACT U]	10 nF [C1210C103KARACT U]	10 nF [C2225C103K2GACT U]
10 nF [C0805F103K2RACT U]	10 nF [C1206C103K4RACT U]	10 nF [C1812C103K1GACT U]	10 nF [C2225C103KCGAC TU]
10 nF [C0805F103K3RACT U]	10 nF [C1206C103K5HACT U]	10 nF [C1812C103K1RACT U]	10 nF [CA064C103K3RACT U]
10 nF [C0805F103K4RACT U]	10 nF [C1206C103K5RACT U]	10 nF [C1812C103K2RACT U]	10 nF [CA064C103K4RACT U]
10 nF [C0805F103K5RACT U]	10 nF [C1206C103KARACT U]	10 nF [C1812C103K5GACT U]	10 nF [CA064C103K5RACT U]
10 nF [C1206C103K1HACT U]	10 nF [C1206C103M1UAC TU]	10 nF [C1812C103K5RACT U]	10 nF [CA064C103K8RACT U]
10 nF [C1206C103K1RACT U]	10 nF [C1206C103M5UAC TU]	10 nF [C1825C103K1GACT U]	10 pF [C0402C100K3GACT U]
10 nF [C1206C103K2RACT U]	10 nF [C1210C103K1RACT U]	10 nF [C1825C103K2GACT U]	10 pF [C0402C100K4GACT U]
10 nF [C1206C103K3GACT U]	10 nF [C1210C103K2RACT U]	10 nF [C1825C103K5GACT U]	10 pF [C0402C100K5GACT U]
10 nF [C1206C103K3HACT U]	10 nF [C1210C103K5GACT U]	10 nF [C2220C103K1GACT U]	10 pF [C0402C100K8GACT U]
10 nF [C1206C103K3RACT U]	10 nF [C1210C103K5RACT U]	10 nF [C2220C103K2GACT U]	10 pF [C0603C100K1GACT U]

# Multisim 14.0 Education Components

---

10 pF [C0603C100K2GACT U]	10 pF [C1206C100K5GACT U]	10 pF [CA064C100K4GAC TU]	10 uF [C1206C106K8PACT U]
10 pF [C0603C100K3GACT U]	10 pF [C1206C100KBGAC TU]	10 pF [CA064C100K5GAC TU]	10 uF [C1206C106K8RACT U]
10 pF [C0603C100K5GACT U]	10 pF [C1210C100K2GACT U]	10 uF [A700V106M016AT E045]	10 uF [C1206C106K9PACT U]
10 pF [C0805C100K1GACT U]	10 pF [C1210C100K5GACT U]	10 uF [A700V106M12RAT E060]	10 uF [C1206C106K9RACT U]
10 pF [C0805C100K2GACT U]	10 pF [C1210C100KBGAC TU]	10 uF [C0805C106K4PACT U]	10 uF [C1206C106M8VAC TU]
10 pF [C0805C100K5GACT U]	10 pF [C1812C100KBGAC TU]	10 uF [C0805C106K8PACT U]	10 uF [C1206C106M9VAC TU]
10 pF [C0805C100KBGAC TU]	10 pF [C1825C100KBGAC TU]	10 uF [C0805C106K9PACT U]	10 uF [C1210C106K3PACT U]
10 pF [C0805C100KDGAC TU]	10 pF [C2220C100KBGAC TU]	10 uF [C0805C106M9VAC TU]	10 uF [C1210C106K3RACT U]
10 pF [C0805H100K5GAC TU]	10 pF [C2225C100KBGAC TU]	10 uF [C1206C106K3PACT U]	10 uF [C1210C106K4PACT U]
10 pF [C1206C100K1GACT U]	10 pF [CA064C100K1GAC TU]	10 uF [C1206C106K4PACT U]	10 uF [C1210C106K4RACT U]
10 pF [C1206C100K2GACT U]	10 pF [CA064C100K2GAC TU]	10 uF [C1206C106K4RACT U]	10 uF [C1210C106K8NAC TU]

# Multisim 14.0 Education Components

---

10 uF [C1210C106K8PACT U]	10 uF [T491A106M016AT]	10 uF [T491D106M050AT ]	10 uF [T494A106M010AT]
10 uF [C1210C106K8RACT U]	10 uF [T491A106M020AT]	10 uF [T491S106M004AT]	10 uF [T494A106M016AT]
10 uF [C1210C106K9PACT U]	10 uF [T491B106M004AT]	10 uF [T491S106M006AT]	10 uF [T494A106M020AT]
10 uF [C1210C106K9RACT U]	10 uF [T491B106M010AT]	10 uF [T491S106M010AT]	10 uF [T494B106M004AT]
10 uF [C1210C106K9RACT U]	10 uF [T491B106M016AT]	10 uF [T491T106M006AT]	10 uF [T494B106M006AT]
10 uF [C1210C106M4VAC TU]	10 uF [T491B106M020AT]	10 uF [T491T106M010AT]	10 uF [T494B106M010AT]
10 uF [C1210C106M8VAC TU]	10 uF [T491C106M010AT]	10 uF [T491T106M016AT]	10 uF [T494B106M020AT]
10 uF [C1210C106M9VAC TU]	10 uF [T491C106M016AT]	10 uF [T491U106M016AT ]	10 uF [T494C106M010AT]
10 uF [T429E106M020AH 4250]	10 uF [T491C106M020AT]	10 uF [T491U106M020AT ]	10 uF [T494C106M016AT]
10 uF [T429H106M035AH 4250]	10 uF [T491C106M025AT]	10 uF [T491V106M035AT]	10 uF [T494C106M020AT]
10 uF [T491A106M004AT]	10 uF [T491C106M035AT]	10 uF [T491X106M050AT]	10 uF [T494C106M025AT]
10 uF [T491A106M006AT]	10 uF [T491D106M025AT ]	10 uF [T493C106M020AH 6110]	10 uF [T494C106M035AT]
10 uF [T491A106M010AT]	10 uF [T491D106M035AT ]	10 uF [T494A106M004AT]	10 uF [T494D106M025AT ]
		10 uF [T494A106M006AT]	10 uF [T494D106M035AT ]

# Multisim 14.0 Education Components

---

10 uF [T494D106M050AT ]	10 uF [T495B106M020AT E1K0]	10 uF [T495X106M050AT E250]	10 uF [T498D106M035AT E700]
10 uF [T494S106M004AT]	10 uF [T495C106M020AT E400]	10 uF [T495X106M050AT E260]	10 uF [T498D106M050AT E1K0]
10 uF [T494S106M006AT]	10 uF [T495C106M020AT E475]	10 uF [T495X106M050AT E300]	10 uF [T510X106M050AT E090]
10 uF [T494S106M010AT]	10 uF [T495C106M025AT E275]	10 uF [T496D106M025AT 6110]	10 uF [T510X106M050AT E120]
10 uF [T494T106M006AT]	10 uF [T495C106M025AT E450]	10 uF [T497F106M015AT 6110]	10 uF [T520A106M010AT E080]
10 uF [T494T106M010AT]	10 uF [T495D106M035AT E125]	10 uF [T498B106M006AT E2K1]	10 uF [T520B106M016AT E100]
10 uF [T494U106M016AT ]	10 uF [T495D106M035AT E250]	10 uF [T498B106M010AT E1K8]	10 uF [T521D106M050AT E090]
10 uF [T494U106M020AT ]	10 uF [T495D106M035AT E300]	10 uF [T498B106M016AT E2K8]	10 uF [T521X106M063AT E050]
10 uF [T494V106M035AT]	10 uF [T495T106M016AT E4K0]	10 uF [T498C106M016AT E1K4]	10 uF [T541X106M063AH 6510]
10 uF [T494X106M050AT]	10 uF [T495X106M035AT E200]	10 uF [T498C106M020AT E1K1]	10_AMP
10 uF [T495A106M010AT E1K8]	10 uF [T495X106M035AT E250]	10 uF [T498C106M025AT E1K1]	100 nF [C0201C104K9PACT U]
10 uF [T495B106M010AT E750]			100 nF [C0402C104K4PACT U]

# Multisim 14.0 Education Components

---

100 nF [C0402C104K4RACT U]	100 nF [C0603C104M4VAC TU]	100 nF [C0805C104M5VAC TU]	100 nF [C1206F104K1RACT U]
100 nF [C0402C104K8PACT U]	100 nF [C0603C104M8VAC TU]	100 nF [C1206C104K1RACT U]	100 nF [C1206F104K2RACT U]
100 nF [C0402C104K8RACT U]	100 nF [C0805C104K1RACT U]	100 nF [C1206C104K2RACT U]	100 nF [C1206F104K3RACT U]
100 nF [C0402C104K9PACT U]	100 nF [C0805C104K3RACT U]	100 nF [C1206C104K3GACT U]	100 nF [C1206F104K4RACT U]
100 nF [C0402C104K9RACT U]	100 nF [C0805C104K4RACT U]	100 nF [C1206C104K3HACT U]	100 nF [C1206F104K5RACT U]
100 nF [C0603C104K3RACT U]	100 nF [C0805C104K5RACT U]	100 nF [C1206C104K3RACT U]	100 nF [C1210C104K1GACT U]
100 nF [C0603C104K4RACT U]	100 nF [C0805C104K8RACT U]	100 nF [C1206C104K4RACT U]	100 nF [C1210C104K1HACT U]
100 nF [C0603C104K5RACT U]	100 nF [C0805C104K9RACT U]	100 nF [C1206C104K5RACT U]	100 nF [C1210C104K1RACT U]
100 nF [C0603C104K8RACT U]	100 nF [C0805C104M3VAC TU]	100 nF [C1206C104KARACT U]	100 nF [C1210C104K2RACT U]
100 nF [C0603C104K9RACT U]	100 nF [C0805C104M4VAC TU]	100 nF [C1206C104M1UAC TU]	100 nF [C1210C104K3GACT U]
100 nF [C0603C104M3VAC TU]	100 nF [C0805C104M5UAC TU]	100 nF [C1206C104M5UAC TU]	100 nF [C1210C104K3HACT U]

# Multisim 14.0 Education Components

---

100 nF [C1210C104K3RACT U]	100 nF [C1210F104K3RACT U]	100 nF [C1812C104M1UAC TU]	100 nF [C2225C104K2RACT U]
100 nF [C1210C104K4RACT U]	100 nF [C1210F104K4RACT U]	100 nF [C1812F104K1RACT U]	100 nF [C2225C104K5RACT U]
100 nF [C1210C104K5GACT U]	100 nF [C1210F104K5RACT U]	100 nF [C1812F104K2RACT U]	100 nF [CA064C104K4RACT U]
100 nF [C1210C104K5HACT U]	100 nF [C1812C104K1GACT U]	100 nF [C1812F104K3RACT U]	100 nF [CA064C104K8RACT U]
100 nF [C1210C104K5RACT U]	100 nF [C1812C104K1HACT U]	100 nF [C1812F104K5RACT U]	100 nF [T491A104M035AT]
100 nF [C1210C104K8RACT U]	100 nF [C1812C104K1R1C7 186]	100 nF [C1825C104K1RACT U]	100 nF [T491A104M050AT]
100 nF [C1210C104KARACT U]	100 nF [C1812C104K1RACT U]	100 nF [C1825C104K2RACT U]	100 nF [T494A104M035AT]
100 nF [C1210C104M1UAC TU]	100 nF [C1812C104K2RACT U]	100 nF [C2220C104K1GACT U]	100 pF [03028BR101AKZC]
100 nF [C1210C104M5UAC TU]	100 nF [C1812C104K5GACT U]	100 nF [C2220C104K2GACT U]	100 pF [C0201C101K3GACT U]
100 nF [C1210F104K1RACT U]	100 nF [C1812C104K5HACT U]	100 nF [C2220C104K5GACT U]	100 pF [C0402C101K1HACT U]
100 nF [C1210F104K2RACT U]	100 nF [C1812C104K5RACT U]	100 nF [C2225C104K1RACT U]	100 pF [C0402C101K3GACT U]



# Multisim 14.0 Education Components

---

100 pF [C0402C101K3HACT U]	100 pF [C0805C101K1GACT U]	100 pF [C1206C101K3GACT U]	100 pF [C1812C101KDGAC TU]
100 pF [C0402C101K4GACT U]	100 pF [C0805C101K2GACT U]	100 pF [C1206C101K5GACT U]	100 pF [C1812C101KHGAC TU]
100 pF [C0402C101K5GACT U]	100 pF [C0805C101K3GACT U]	100 pF [C1206C101KBGAC TU]	100 pF [C1825C101KBGAC TU]
100 pF [C0402C101K5HACT U]	100 pF [C0805C101K4GACT U]	100 pF [C1206C101KCGAC TU]	100 pF [C2220C101KBGAC TU]
100 pF [C0402C101K8GACT U]	100 pF [C0805C101K5GACT U]	100 pF [C1206C101KDGAC TU]	100 pF [C2225C101KBGAC TU]
100 pF [C0603C101K1GACT U]	100 pF [C0805C101KBGAC TU]	100 pF [C1206C101KGGAC TU]	100 pF [CA064C101K1GAC TU]
100 pF [C0603C101K3GACT U]	100 pF [C0805C101KCGAC TU]	100 pF [C1210C101K5GACT U]	100 pF [CA064C101K3GAC TU]
100 pF [C0603C101K4GACT U]	100 pF [C0805C101KDGAC TU]	100 pF [C1210C101KBGAC TU]	100 pF [CA064C101K5GAC TU]
100 pF [C0603C101K5GACT U]	100 pF [C0805H101K5GAC TU]	100 pF [C1210C101KCGAC TU]	100 pF [CA064C101K8GAC TU]
100 pF [C0603C101K5RACT U]	100 pF [C1206C101K1GACT U]	100 pF [C1210C101KDGAC TU]	100 uF [A700D107M006AT E015]
100 pF [C0603C101K8GACT U]	100 pF [C1206C101K2GACT U]	100 pF [C1812C101KBGAC TU]	100 uF [A700D107M006AT E018]

# Multisim 14.0 Education Components

---

100 uF [A700V107M002AT E018]	100 uF [T491B107M006AT]	100 uF [T491U107M004AT ]	100 uF [T494D107M004AT ]
100 uF [A700V107M002AT E025]	100 uF [T491B107M010AT]  100 uF [T491C107M004AT]	100 uF [T491U107M006AT ]	100 uF [T494D107M006AT ]
100 uF [A700V107M002AT E028]	100 uF [T491C107M006AT]	100 uF [T491V107M006AT]	100 uF [T494D107M010AT ]
100 uF [A700X107M008AT E010]	100 uF [T491C107M010AT]  100 uF [T491D107M004AT ]	100 uF [T491V107M010AT]  100 uF [T491V107M016AT]	100 uF [T494D107M016AT ]
100 uF [A700X107M008AT E015]	100 uF [T491D107M006AT ]	100 uF [T491X107M016AT]	100 uF [T494E107M020AT]
100 uF [A700X107M010AT E010]	100 uF [T491D107M010AT ]	100 uF [T491X107M020AT]	100 uF [T494T107M004AT]
100 uF [A700X107M010AT E015]	100 uF [T491D107M016AT ]	100 uF [T491X107M025AT]	100 uF [T494T107M2R5AT]
100 uF [T489C107M010AT E500]	100 uF [T491D107M020AT ]	100 uF [T494A107M004AT]	100 uF [T494U107M004AT ]
100 uF [T489D107M010AT E150]	100 uF [T491E107M020AT]	100 uF [T494B107M004AT]	100 uF [T494U107M006AT ]
100 uF [T489D107M010AT E440]	100 uF [T491T107M004AT]	100 uF [T494B107M006AT]	100 uF [T494V107M006AT]
100 uF [T491A107M004AT]	100 uF [T491T107M2R5AT]	100 uF [T494C107M004AT]	100 uF [T494V107M010AT]
100 uF [T491B107M004AT]		100 uF [T494C107M006AT]	100 uF [T494V107M016AT]
		100 uF [T494C107M010AT]	100 uF [T494X107M016AT]

# Multisim 14.0 Education Components

---

100 uF [T494X107M020AT]	100 uF [T495D107M016AT E100]	100 uF [T495X107M020AT E100]	100 uF [T520B107M003AT E035]
100 uF [T494X107M025AT]	100 uF [T495D107M016AT E125]	100 uF [T495X107M020AT E150]	100 uF [T520B107M003AT E040]
100 uF [T495B107M006AT E400]	100 uF [T495E107M020AT E060]	100 uF [T498D107M006AT E600]	100 uF [T520B107M003AT E070]
100 uF [T495B107M006AT E700]	100 uF [T495E107M020AT E200]	100 uF [T498D107M010AT E600]	100 uF [T520B107M004AT E035]
100 uF [T495B107M010AT E350]	100 uF [T495T107M2R5AT E3K0]	100 uF [T510E107M025AT E050]	100 uF [T520B107M004AT E040]
100 uF [T495C107M006AT E150]	100 uF [T495V107M006AT E150]	100 uF [T510X107M020AT E040]	100 uF [T520B107M004AT E070]
100 uF [T495D107M006AT E050]	100 uF [T495V107M010AT E100]	100 uF [T510X107M020AT E045]	100 uF [T520B107M006AT E015]
100 uF [T495D107M006AT E130]	100 uF [T495V107M010AT E150]	100 uF [T513D107M016AH 6110]	100 uF [T520B107M006AT E018]
100 uF [T495D107M010AT E050]	100 uF [T495X107M010AT E100]	100 uF [T513E107M025AH 6110]	100 uF [T520B107M006AT E025]
100 uF [T495D107M010AT E065]	100 uF [T495X107M016AT E080]	100 uF [T513X107M020AH 6110]	100 uF [T520B107M006AT E035]
100 uF [T495D107M010AT E080]	100 uF [T495X107M016AT E100]	100 uF [T513X107M020AH 6120]	100 uF [T520B107M006AT E040]

# Multisim 14.0 Education Components

---

100 uF [T520B107M006AT E070]	100 uF [T520T107M004AT E070]	100 uF [T520V107M010AT E025]	100 uF [T525D107M010AT E055]
100 uF [T520B107M2R5AT E035]	100 uF [T520T107M004AT E150]	100 uF [T520V107M010AT E045]	100 uF [T525T107M2R5AT E080]
100 uF [T520B107M2R5AT E040]	100 uF [T520T107M006AT E070]	100 uF [T520V107M010AT E050]	100 uF [T528I107M003ATE 200]
100 uF [T520C107M006AT E025]	100 uF [T520T107M2R5AT E070]	100 uF [T520W107M006AT E040]	100 uF [T540B107M004AH 6510]
100 uF [T520C107M006AT E045]	100 uF [T520U107M004AT E055]	100 uF [T520W107M010AT E040]	100 uF [T540D107M010AH 6510]
100 uF [T520C107M010AT E025]	100 uF [T520U107M006AT E055]	100 uF [T521D107M016AT E050]	10029449-001RLF  100V_100W
100 uF [T520C107M010AT E045]	100 uF [T520V107M006AT E007]	100 uF [T521V107M016AT E050]	10104111-0001LF  105081-0001
100 uF [T520D107M006AT E007]	100 uF [T520V107M006AT E009]	100 uF [T521X107M025AT E060]	10BQ015  10BQ040
100 uF [T520D107M010AT E018]	100 uF [T520V107M006AT E012]	100 uF [T525B107M003AT E080]	10Line_Bussed  10Line_Isolated
100 uF [T520D107M010AT E055]	100 uF [T520V107M006AT E045]	100 uF [T525B107M004AT E080]	10TQ045  10YQ045
100 uF [T520D107M010AT E080]	100 uF [T520V107M010AT E018]	100 uF [T525D107M010AT E025]	10YQ045C  11 pF [C0805C110KBGAC TU]

# Multisim 14.0 Education Components

---

11 pF [C1206C110KBGAC TU]	110 pF [C1206C111K5GACT U]	12 nF [C0402C123K9PACT U]	12 nF [C0805C123K4RACT U]
11 pF [C1210C110KBGAC TU]	110 pF [C1206C111KBGAC TU]	12 nF [C0402C123K9RACT U]	12 nF [C0805C123K5GACT U]
11 pF [C1812C110KBGAC TU]	110 pF [C1210C111KBGAC TU]	12 nF [C0603C123K1RACT U]	12 nF [C0805C123K5HACT U]
11 pF [C1825C110KBGAC TU]	110 pF [C1812C111KBGAC TU]	12 nF [C0603C123K3RACT U]	12 nF [C0805C123K5RACT U]
11 pF [C2220C110KBGAC TU]	110 pF [C1825C111KBGAC TU]	12 nF [C0603C123K4RACT U]	12 nF [C0805C123K8RACT U]
11 pF [C2225C110KBGAC TU]	110 pF [C2220C111KBGAC TU]	12 nF [C0603C123K5RACT U]	12 nF [C0805C123KARACT U]
110 pF [C0402C111K1HACT U]	110 pF [C2225C111KBGAC TU]	12 nF [C0805C123K1GACT U]	12 nF [C0805F123K1RACT U]
110 pF [C0402C111K3HACT U]	12 nF [C0402C123K4RACT U]	12 nF [C0805C123K1HACT U]	12 nF [C0805F123K3RACT U]
110 pF [C0402C111K5HACT U]	12 nF [C0402C123K5RACT U]	12 nF [C0805C123K1RACT U]	12 nF [C0805F123K4RACT U]
110 pF [C0603C111K5GACT U]	12 nF [C0402C123K8PACT U]	12 nF [C0805C123K3HACT U]	12 nF [C0805F123K5RACT U]
110 pF [C0805C111K1GACT U]	12 nF [C0402C123K8RACT U]	12 nF [C0805C123K3RACT U]	12 nF [C1206C123K1HACT U]

# Multisim 14.0 Education Components

---

12 nF [C1206C123K1RACT U]	12 nF [C1210C123K5HACT U]	12 pF [C0603C120K5GACT U]	12 pF [C2225C120KBGAC TU]
12 nF [C1206C123K2RACT U]	12 nF [C1210C123K5RACT U]	12 pF [C0805C120K1GACT U]	12 pF [CA064C120K5GAC TU]
12 nF [C1206C123K3HACT U]	12 nF [C1210C123KARACT U]	12 pF [C0805C120K5GACT U]	12 uF [C1210C126K8PACT U]
12 nF [C1206C123K5HACT U]	12 nF [C1812C123K1RACT U]	12 pF [C0805C120KBGAC TU]	120 nF [C0603C124K4RACT U]
12 nF [C1206C123K5RACT U]	12 nF [C2220C123K2GACT U]	12 pF [C1206C120K1GACT U]	120 nF [C0603C124K8RACT U]
12 nF [C1206C123KARACT U]	12 pF [C0201C120K3GACT U]	12 pF [C1206C120K5GACT U]	120 nF [C0805C124K1RACT U]
12 nF [C1210C123K1GACT U]	12 pF [C0402C120K4GACT U]	12 pF [C1206C120KBGAC TU]	120 nF [C0805C124K3RACT U]
12 nF [C1210C123K1HACT U]	12 pF [C0402C120K5GACT U]	12 pF [C1210C120KBGAC TU]	120 nF [C0805C124K4RACT U]
12 nF [C1210C123K3HACT U]	12 pF [C0603C120K1GACT U]	12 pF [C1812C120KBGAC TU]	120 nF [C0805C124K5RACT U]
12 nF [C1210C123K4RACT U]	12 pF [C0603C120K2GACT U]	12 pF [C1825C120KBGAC TU]	120 nF [C0805C124K8RACT U]
12 nF [C1210C123K5GACT U]	12 pF [C0603C120K3GACT U]	12 pF [C2220C120KBGAC TU]	120 nF [C1206C124K1RACT U]

# Multisim 14.0 Education Components

---

120 nF [C1206C124K2RACT U]	120 nF [C1210F124K4RACT U]	120 nF [C1812F124K3RACT U]	120 pF [C0603C121K5GACT U]
120 nF [C1206C124K3RACT U]	120 nF [C1210F124K5RACT U]	120 nF [C1812F124K5RACT U]	120 pF [C0805C121K1GACT U]
120 nF [C1206C124K4RACT U]	120 nF [C1812C124K1GACT U]	120 nF [C2220C124K1GACT U]	120 pF [C0805C121K2GACT U]
120 nF [C1206C124K5RACT U]	120 nF [C1812C124K1HACT U]	120 nF [C2220C124K5GACT U]	120 pF [C0805C121K5GACT U]
120 nF [C1206C124M5UAC TU]	120 nF [C1812C124K2RACT U]	120 nF [C2225C124K1RACT U]	120 pF [C1206C121K1GACT U]
120 nF [C1210C124K1RACT U]	120 nF [C1812C124K5GACT U]	120 pF [03029BR121AKZC] U]	120 pF [C1206C121K2GACT U]
120 nF [C1210C124K3HACT U]	120 nF [C1812C124K5HACT U]	120 pF [C0402C121K1HACT U]	120 pF [C1206C121K5GACT U]
120 nF [C1210C124K5HACT U]	120 nF [C1812C124K5RACT U]	120 pF [C0402C121K3HACT U]	120 pF [C1206C121KBGAC TU]
120 nF [C1210C124K5RACT U]	120 nF [C1812C124M1UAC TU]	120 pF [C0402C121K5GACT U]	120 pF [C1206C121KDGAC TU]
120 nF [C1210F124K1RACT U]	120 nF [C1812F124K1RACT U]	120 pF [C0402C121K5HACT U]	120 pF [C1210C121KBGAC TU]
120 nF [C1210F124K3RACT U]	120 nF [C1812F124K2RACT U]	120 pF [C0603C121K1GACT U]	120 pF [C1812C121KBGAC TU]

# Multisim 14.0 Education Components

---

120 pF [C1825C121KBGAC TU]	120 uF [A700X127M010AT E015]	12V_AC_NC_RELAY _VIRTUAL	13 pF [C2225C130KBGAC TU]
120 pF [C2220C121KBGAC TU]	120 uF [T520B127M006AT E035]	12V_AC_NO_RELAY _VIRTUAL	130 pF [C0402C131K1HACT U]
120 pF [C2225C121KBGAC TU]	120LQ045	12V_AC_NONC_RELAY_VIRTUAL	130 pF [C0402C131K3HACT U]
120 pF [CA064C121K5GAC TU]	120LQ100	13 pF [C0603C130K2GACT U]	130 pF [C0402C131K5HACT U]
120 uF [A700D127M004AT E015]	120V_100W	13 pF [C0603C130K5GACT U]	130 pF [C0805H131K3GAC TU]
120 uF [A700D127M004AT E018]	120V_250W	13 pF [C0805C130K5GACT U]	130 pF [C1206C131KBGAC TU]
120 uF [A700D127M006AT E012]	120V_AC_NC_RELAY_VIRTUAL	13 pF [C1206C130KBGAC TU]	130 pF [C1812C131KBGAC TU]
120 uF [A700D127M006AT E015]	120V_AC_NO_RELAY_VIRTUAL	13 pF [C1812C130KBGAC TU]	130 pF [C1825C131KBGAC TU]
120 uF [A700D127M006AT E018]	120V_AC_NONC_RELAY_VIRTUAL	13 pF [C1825C130KBGAC TU]	130 pF [C2220C131KBGAC TU]
120 uF [A700V127M002AT E018]	1-282834-0	13 pF [C2220C130KBGAC TU]	130 pF [C2225C131KBGAC TU]
120 uF [A700X127M010AT E010]	12A02CH-TL-E		
	12A02MH-TL-E		
	12AU7A		
	12AX7A		
	12BH7A		
	12CGQ150		
	12CTQ045		
	12TQ045		
	12V_10W		
	12V_25W		



# Multisim 14.0 Education Components

---

15 nF [C0402C153K4RACT U]	15 nF [C0805C153K1HACT U]	15 nF [C0805F153K1RACT U]	15 nF [C1206C153KARACT U]
15 nF [C0402C153K5RACT U]	15 nF [C0805C153K1RACT U]	15 nF [C0805F153K3RACT U]	15 nF [C1206C153M5UAC TU]
15 nF [C0402C153K8PACT U]	15 nF [C0805C153K3HACT U]	15 nF [C0805F153K4RACT U]	15 nF [C1210C153K1GACT U]
15 nF [C0402C153K8RACT U]	15 nF [C0805C153K3RACT U]	15 nF [C0805F153K5RACT U]	15 nF [C1210C153K1HACT U]
15 nF [C0402C153K9PACT U]	15 nF [C0805C153K4RACT U]	15 nF [C1206C153K1HACT U]	15 nF [C1210C153K1RACT U]
15 nF [C0402C153K9RACT U]	15 nF [C0805C153K5GACT U]	15 nF [C1206C153K1RACT U]	15 nF [C1210C153K2RACT U]
15 nF [C0603C153K1RACT U]	15 nF [C0805C153K5HACT U]	15 nF [C1206C153K2RACT U]	15 nF [C1210C153K3HACT U]
15 nF [C0603C153K3RACT U]	15 nF [C0805C153K5RACT U]	15 nF [C1206C153K3HACT U]	15 nF [C1210C153K5HACT U]
15 nF [C0603C153K4RACT U]	15 nF [C0805C153K8RACT U]	15 nF [C1206C153K4RACT U]	15 nF [C1210C153K5RACT U]
15 nF [C0603C153K5RACT U]	15 nF [C0805C153KARACT U]	15 nF [C1206C153K5HACT U]	15 nF [C1210C153KARACT U]
15 nF [C0805C153K1GACT U]	15 nF [C0805C153M5UAC TU]	15 nF [C1206C153K5RACT U]	15 nF [C1812C153K1GACT U]

# Multisim 14.0 Education Components

---

15 nF [C1812C153K1HACT U]	15 pF [C0402C150K3GACT U]	15 pF [C0805C150K4GACT U]	15 pF [C2220C150KBGAC TU]
15 nF [C1812C153K1RACT U]	15 pF [C0402C150K4GACT U]	15 pF [C0805C150K5GACT U]	15 pF [C2225C150KBGAC TU]
15 nF [C1812C153K2RACT U]	15 pF [C0402C150K5GACT U]	15 pF [C0805C150KBGAC TU]	15 pF [CA064C150K4GAC TU]
15 nF [C1812C153K5GACT U]	15 pF [C0402C150K8GACT U]	15 pF [C1206C150K1GACT U]	15 pF [CA064C150K5GAC TU]
15 nF [C1812C153K5HACT U]	15 pF [C0603C150K1GACT U]	15 pF [C1206C150K2GACT U]	15 uF [A700V156M12RAT E040]
15 nF [C1812C153K5RACT U]	15 pF [C0603C150K2GACT U]	15 pF [C1206C150K5GACT U]	15 uF [C1210C156K4PACT U]
15 nF [C1825C153K5GACT U]	15 pF [C0603C150K4GACT U]	15 pF [C1206C150KBGAC TU]	15 uF [C1210C156K8PACT U]
15 nF [C2220C153K2GACT U]	15 pF [C0603C150K5GACT U]	15 pF [C1206C150KGGAC TU]	15 uF [C1210C156K9PACT U]
15 nF [C2225C153K5GACT U]	15 pF [C0805C150K1GACT U]	15 pF [C1210C150KBGAC TU]	15 uF [T409E156M004AH 4250]
15 nF [CA064C153K5RACT U]	15 pF [C0805C150K2GACT U]	15 pF [C1812C150KBGAC TU]	15 uF [T409H156M025AH 4250]
15 pF [C0201C150K3GACT U]	15 pF [C0805C150K3GACT U]	15 pF [C1825C150KBGAC TU]	15 uF [T419B156M004AH 4250]

# Multisim 14.0 Education Components

---

15 uF [T419D156M010AH 4250]	15 uF [T491C156M006AT]	15 uF [T491U156M016AT ]	15 uF [T494C156M025AT]
15 uF [T429B156M004AH 4250]	15 uF [T491C156M010AT]	15 uF [T491X156M035AT]	15 uF [T494D156M020AT ]
15 uF [T429F156M010AH 4250]	15 uF [T491C156M016AT]	15 uF [T491X156M050AT]	15 uF [T494D156M025AT ]
15 uF [T429F156M020AH 4250]	15 uF [T491C156M025AT]	15 uF [T494A156M004AT]	15 uF [T494D156M035AT ]
15 uF [T489D156M025AT E300]	15 uF [T491D156M020AT ]	15 uF [T494A156M006AT]	15 uF [T494S156M004AT]
15 uF [T491A156M004AT]	15 uF [T491D156M025AT ]	15 uF [T494A156M010AT]	15 uF [T494S156M006AT]
15 uF [T491A156M006AT]	15 uF [T491D156M035AT ]	15 uF [T494B156M004AT]	15 uF [T494T156M004AT]
15 uF [T491A156M010AT]	15 uF [T491S156M004AT]	15 uF [T494B156M006AT]	15 uF [T494T156M006AT]
15 uF [T491A156M016AT]	15 uF [T491S156M006AT]	15 uF [T494B156M010AT]	15 uF [T494T156M010AT]
15 uF [T491B156M004AT]	15 uF [T491T156M004AT]	15 uF [T494B156M016AT]	15 uF [T494U156M010AT ]
15 uF [T491B156M006AT]	15 uF [T491T156M006AT]	15 uF [T494B156M025AT]	15 uF [T494U156M016AT ]
15 uF [T491B156M010AT]	15 uF [T491T156M010AT]	15 uF [T494C156M006AT]	15 uF [T494U156M016AT ]
15 uF [T491B156M016AT]	15 uF [T491U156M010AT ]	15 uF [T494C156M010AT]	15 uF [T494X156M035AT]
15 uF [T491B156M025AT]		15 uF [T494C156M016AT]	15 uF [T494X156M050AT]
		15 uF [T494C156M020AT]	

# Multisim 14.0 Education Components

---

15 uF [T495B156M010AT E500]	15 uF [T495X156M050AT E300]	15 uF [T520D156M025AT E060]	15 uF [T541X156M063AH 6510]
15 uF [T495C156M010AT E375]	15 uF [T497E156M010AT 6110]	15 uF [T520D156M025AT E080]	15 uF [T543T156M006AT E100]
15 uF [T495C156M010AT E400]	15 uF [T498B156M006AT E1K8]	15 uF [T520T156M004AT E100]	15_AMP  150 nF [C0603C154K4RACT U]
15 uF [T495D156M020AT E275]	15 uF [T498B156M010AT E1K5]	15 uF [T520T156M006AT E100]	150 nF [C0603C154K5RACT U]
15 uF [T495D156M025AT E100]	15 uF [T498C156M010AT E1K8]	15 uF [T520T156M12RAT E080]	150 nF [C0603C154K8RACT U]
15 uF [T495D156M025AT E275]	15 uF [T498C156M016AT E1K1]	15 uF [T521B156M016AT E090]	150 nF [C0603C154M3VAC TU]
15 uF [T495D156M035AT E225]	15 uF [T498D156M025AT E700]	15 uF [T521V156M025AT E090]	150 nF [C0603C154M4VAC TU]
15 uF [T495D156M035AT E300]	15 uF [T499B156M006AT E3K5]	15 uF [T521V156M035AT E100]	150 nF [C0603C154M8VAC TU]
15 uF [T495X156M025AT E200]	15 uF [T499D156M020AT E1K0]	15 uF [T521V156M035AT E125]	150 nF [C0805C154K3RACT U]
15 uF [T495X156M035AT E200]	15 uF [T513D156M035AH 6110]	15 uF [T521X156M063AT E035]	150 nF [C0805C154K4RACT U]
15 uF [T495X156M050AT E200]	15 uF [T520A156M010AT E080]	15 uF [T521X156M063AT E150]	150 nF [C0805C154K5RACT U]

# Multisim 14.0 Education Components

---

150 nF [C0805C154K8RACT U]	150 nF [C1206F154K5RACT U]	150 nF [C1812C154K1RACT U]	150 nF [C1825C154K1RACT U]
150 nF [C0805C154M3VAC TU]	150 nF [C1210C154K1RACT U]	150 nF [C1812C154K2RACT U]	150 nF [C1825C154K5RACT U]
150 nF [C1206C154K1RACT U]	150 nF [C1210C154K3HACT U]	150 nF [C1812C154K5GACT U]	150 nF [C2220C154K1GACT U]
150 nF [C1206C154K2RACT U]	150 nF [C1210C154K5HACT U]	150 nF [C1812C154K5HACT U]	150 nF [C2220C154K5GACT U]
150 nF [C1206C154K3RACT U]	150 nF [C1210C154K5RACT U]	150 nF [C1812C154K5RACT U]	150 nF [C2225C154K1RACT U]
150 nF [C1206C154K4RACT U]	150 nF [C1210F154K1RACT U]	150 nF [C1812C154M1UAC TU]	150 nF [C2225C154K2RACT U]
150 nF [C1206C154K5RACT U]	150 nF [C1210F154K3RACT U]	150 nF [C1812C154M5UAC TU]	150 nF [T429A154M050AH 4250]
150 nF [C1206C154M5UAC TU]	150 nF [C1210F154K4RACT U]	150 nF [C1812F154K1RACT U]	150 nF [T491A154M035AT]
150 nF [C1206F154K1RACT U]	150 nF [C1210F154K5RACT U]	150 nF [C1812F154K2RACT U]	150 nF [T491A154M050AT]
150 nF [C1206F154K3RACT U]	150 nF [C1812C154K1GACT U]	150 nF [C1812F154K3RACT U]	150 nF [T491B154M050AT]
150 nF [C1206F154K4RACT U]	150 nF [C1812C154K1HACT U]	150 nF [C1812F154K5RACT U]	150 nF [T494A154M035AT]
			150 nF [T494A154M050AT]
			150 nF [T494B154M050AT]

# Multisim 14.0 Education Components

---

150 pF [C0402C151K1HACT U]	150 pF [C0603C151K5GACT U]	150 pF [C1812C151KBGAC TU]	150 uF [A700V157M002AT E018]
150 pF [C0402C151K3HACT U]	150 pF [C0805C151K1GACT U]	150 pF [C1825C151KBGAC TU]	150 uF [A700V157M002AT E025]
150 pF [C0402C151K3RACT U]	150 pF [C0805C151K2GACT U]	150 pF [C2220C151KBGAC TU]	150 uF [A700V157M002AT E028]
150 pF [C0402C151K4RACT U]	150 pF [C0805C151K3GACT U]	150 pF [C2225C151KBGAC TU]	150 uF [A700X157M006AT E010]
150 pF [C0402C151K5GACT U]	150 pF [C0805C151K4GACT U]	150 pF [CA064C151K4GAC TU]	150 uF [A700X157M006AT E015]
150 pF [C0402C151K5HACT U]	150 pF [C0805C151K5GACT U]	150 pF [CA064C151K5GAC TU]	150 uF [A700X157M010AT E010]
150 pF [C0402C151K5RACT U]	150 pF [C1206C151K1GACT U]	150 uF [A700D157M004AT E015]	150 uF [A700X157M010AT E015]
150 pF [C0402C151K8RACT U]	150 pF [C1206C151K2GACT U]	150 uF [A700D157M004AT E018]	150 uF [T429G157M006AH 4250]
150 pF [C0603C151K1GACT U]	150 pF [C1206C151K5GACT U]	150 uF [A700D157M2R5AT E015]	150 uF [T429X157M010AH 4250]
150 pF [C0603C151K3GACT U]	150 pF [C1206C151KBGAC TU]	150 uF [A700D157M2R5AT E018]	150 uF [T491B157M004AT]
150 pF [C0603C151K4GACT U]	150 pF [C1210C151KBGAC TU]	150 uF [A700V157M002AT E009]	150 uF [T491C157M004AT]  150 uF [T491C157M006AT]

# Multisim 14.0 Education Components

---

150 uF [T491C157M010AT]	150 uF [T494C157M010AT]	150 uF [T495D157M006AT E050]	150 uF [T495X157M010AT E085]
150 uF [T491D157M004AT ]	150 uF [T494D157M004AT ]	150 uF [T495D157M006AT E125]	150 uF [T495X157M010AT E100]
150 uF [T491D157M006AT ]	150 uF [T494D157M006AT ]	150 uF [T495D157M010AT E050]	150 uF [T495X157M016AT E075]
150 uF [T491D157M010AT ]	150 uF [T494D157M010AT ]	150 uF [T495D157M010AT E060]	150 uF [T495X157M016AT E100]
150 uF [T491D157M016AT ]	150 uF [T494D157M016AT ]	150 uF [T495D157M010AT E100]	150 uF [T510X157M016AT E030]
150 uF [T491V157M004AT]	150 uF [T494V157M004AT]	150 uF [T495D157M016AT E060]	150 uF [T510X157M016AT E040]
150 uF [T491V157M006AT]	150 uF [T494V157M006AT]	150 uF [T495D157M016AT E085]	150 uF [T513X157M016AH 6110]
150 uF [T491V157M010AT]	150 uF [T494V157M010AT]	150 uF [T495D157M016AT E100]	150 uF [T513X157M016AH 6120]
150 uF [T491X157M010AT]	150 uF [T494X157M010AT]	150 uF [T495D157M016AT E125]	150 uF [T520B157M003AT E025]
150 uF [T491X157M016AT]	150 uF [T494X157M016AT]	150 uF [T495D157M016AT E150]	150 uF [T520B157M003AT E035]
150 uF [T491X157M020AT]	150 uF [T494X157M020AT]	150 uF [T495V157M010AT E150]	150 uF [T520B157M003AT E040]
150 uF [T494B157M004AT]	150 uF [T495B157M004AT E900]		
150 uF [T494C157M004AT]	150 uF [T495C157M006AT E200]		
150 uF [T494C157M006AT]			

# Multisim 14.0 Education Components

---

150 uF [T520B157M003AT E070]	150 uF [T520C157M004AT E015]	150 uF [T520D157M006AT E007]	150 uF [T520L157M006AT E025]
150 uF [T520B157M004AT E015]	150 uF [T520C157M004AT E025]	150 uF [T520D157M006AT E015]	150 uF [T520M157M006AT E070]
150 uF [T520B157M004AT E018]	150 uF [T520C157M004AT E045]	150 uF [T520D157M006AT E025]	150 uF [T520U157M004AT E055]
150 uF [T520B157M004AT E025]	150 uF [T520C157M004AT E100]	150 uF [T520D157M006AT E055]	150 uF [T520U157M006AT E045]
150 uF [T520B157M004AT E030]	150 uF [T520C157M006AT E015]	150 uF [T520D157M008AT E025]	150 uF [T520U157M006AT E055]
150 uF [T520B157M004AT E035]	150 uF [T520C157M006AT E025]	150 uF [T520D157M008AT E040]	150 uF [T520U157M2R5AT E055]
150 uF [T520B157M004AT E040]	150 uF [T520C157M006AT E045]	150 uF [T520D157M008AT E055]	150 uF [T520V157M004AT E007]
150 uF [T520B157M004AT E070]	150 uF [T520C157M006AT E055]	150 uF [T520D157M010AT E025]	150 uF [T520V157M004AT E009]
150 uF [T520B157M006AT E035]	150 uF [T520C157M010AT E055]	150 uF [T520D157M010AT E040]	150 uF [T520V157M004AT E012]
150 uF [T520B157M006AT E045]	150 uF [T520D157M004AT E007]	150 uF [T520D157M010AT E055]	150 uF [T520V157M004AT E015]
150 uF [T520B157M006AT E070]	150 uF [T520D157M006AT E006]	150 uF [T520L157M006AT E012]	150 uF [T520V157M004AT E025]



# Multisim 14.0 Education Components

---

150 uF [T520V157M006AT E006]	150 uF [T520W157M006AT E025]	150 uF [T530D157M010AT E006]	16 pF [C1206C160KBGAC TU]
150 uF [T520V157M006AT E007]	150 uF [T520W157M006AT E040]	150 uF [T530D157M010AT E010]	16 pF [C1210C160KBGAC TU]
150 uF [T520V157M006AT E009]	150 uF [T520X157M016AT E040]	150 uF [T530X157M016AT E015]	16 pF [C1812C160KBGAC TU]
150 uF [T520V157M006AT E012]	150 uF [T522V157M006AT E040]	150 uF [T530X157M016AT E025]	16 pF [C1825C160KBGAC TU]
150 uF [T520V157M006AT E015]	150 uF [T525B157M003AT E080]	150 uF [T530X157M016AT E040]	16 pF [C2220C160KBGAC TU]
150 uF [T520V157M006AT E018]	150 uF [T525D157M006AT E025]	1-534206-0  1-534206-3	16 pF [C2225C160KBGAC TU]
150 uF [T520V157M006AT E025]	150 uF [T525D157M010AT E025]	1-534206-7  15C02MH-TL-E	160 pF [C0402C161K1HACT U]
150 uF [T520V157M006AT E040]	150 uF [T528Z157M006AT E007]	15CGQ100  15CLQ100	160 pF [C0402C161K3HACT U]
150 uF [T520V157M006AT E045]	150 uF [T528Z157M006AT E008]	15LJQ100  16 pF [C0603C160K2GACT U]	160 pF [C0402C161K5HACT U]
150 uF [T520V157M010AT E018]	150 uF [T528Z157M006AT E009]	16 pF [C0603C160K5GACT U]	160 pF [C0805C161K3GACT U]
150 uF [T520V157M010AT E040]	150 uF [T528Z157M006AT E012]	16 pF [C0805C160KBGAC TU]	160 pF [C0805C161K5GACT U]

# Multisim 14.0 Education Components

---

160 pF [C1206C161KBGAC TU]	171-037-113R001	18 nF [C0402C183K4RACT U]	18 nF [C0805C183K3GACT U]
	171-037-213R001		
160 pF [C1210C161KBGAC TU]	171-050-113R001	18 nF [C0402C183K8PACT U]	18 nF [C0805C183K3HACT U]
	171-050-213R001		
160 pF [C1812C161KBGAC TU]	1734035-1	18 nF [C0402C183K8RACT U]	18 nF [C0805C183K4RACT U]
	173-E09-113R001		
	173-E09-213R001		
160 pF [C1825C161KBGAC TU]	173-E15-113R001	18 nF [C0402C183K9PACT U]	18 nF [C0805C183K5HACT U]
	173-E15-213R001		
160 pF [C2220C161KBGAC TU]	173-E25-113R001	18 nF [C0402C183K9RACT U]	18 nF [C0805C183K5RACT U]
	173-E25-213R001		
160 pF [C2225C161KBGAC TU]	173-E37-113R001	18 nF [C0603C183K1RACT U]	18 nF [C0805C183K8RACT U]
	173-E37-213R001		
	173-E50-113R001		
1-640455-0	173-E50-213R001	18 nF [C0603C183K3RACT U]	18 nF [C0805C183KARACT U]
16CYQ100C	174-E09-113R001		
16CYQ150C	174-E09-213R001	18 nF [C0603C183K4RACT U]	18 nF [C0805F183K1RACT U]
16SYQ060C	174-E15-113R001		
16YQ045C	174-E15-213R001	18 nF [C0603C183K5RACT U]	18 nF [C0805F183K3RACT U]
16YQ150C	174-E25-113R001		
171-009-113R001	174-E25-213R001	18 nF [C0603C183K8RACT U]	18 nF [C0805F183K4RACT U]
171-009-213R001	174-E37-113R001		
171-015-113R001	174-E37-213R001	18 nF [C0805C183K1RACT U]	18 nF [C0805F183K5RACT U]
171-015-213R001	174-E50-113R001		
171-025-113R001	174-E50-213R001		
171-025-213R001			

# Multisim 14.0 Education Components

---

18 nF [C1206C183K1HACT U]	18 nF [C1210C183K5HACT U]	18 pF [C0402C180K3GACT U]	18 pF [C0805C180KBGAC TU]
18 nF [C1206C183K1RACT U]	18 nF [C1210C183K5RACT U]	18 pF [C0402C180K5GACT U]	18 pF [C1206C180K1GACT U]
18 nF [C1206C183K2RACT U]	18 nF [C1210C183KARACT U]	18 pF [C0402C180K8GACT U]	18 pF [C1206C180K5GACT U]
18 nF [C1206C183K3GACT U]	18 nF [C1812C183K1GACT U]	18 pF [C0603C180K2GACT U]	18 pF [C1206C180KBGAC TU]
18 nF [C1206C183K3HACT U]	18 nF [C1812C183K1HACT U]	18 pF [C0603C180K3GACT U]	18 pF [C1210C180KBGAC TU]
18 nF [C1206C183K5HACT U]	18 nF [C1812C183K5GACT U]	18 pF [C0603C180K5GACT U]	18 pF [C1812C180KBGAC TU]
18 nF [C1206C183K5RACT U]	18 nF [C1812C183K5HACT U]	18 pF [C0603C180K8GACT U]	18 pF [C1825C180KBGAC TU]
18 nF [C1210C183K1GACT U]	18 nF [C2220C183K2GACT U]	18 pF [C0805C180K1GACT U]	18 pF [C2220C180KBGAC TU]
18 nF [C1210C183K1HACT U]	18 nF [CA064C183K3RAC]  18 nF [CDR03BX183BKSM ]	18 pF [C0805C180K2GACT U]  18 pF [C0805C180K3GACT U]	18 pF [C2225C180KBGAC TU]  18 uF [C1210C186K4PACT U]
18 nF [C1210C183K5GACT U]	18 pF [C0201C180K3GACT U]	18 pF [C0805C180K5GACT U]	18 uF [C1210C186K8PACT U]

# Multisim 14.0 Education Components

---

18 uF [C1210C186K9PACT U]	180 nF [C1206F184K1RACT U]	180 nF [C1812C184K1RACT U]	180 pF [C0402C181K3RACT U]
18 uF [T521X186M050AT E070]	180 nF [C1206F184K3RACT U]	180 nF [C1812C184K5HACT U]	180 pF [C0402C181K4RACT U]
180 nF [C0603C184K4RACT U]	180 nF [C1206F184K4RACT U]	180 nF [C1812C184K5RACT U]	180 pF [C0402C181K5HACT U]
180 nF [C0603C184K8RACT U]	180 nF [C1206F184K5RACT U]	180 nF [C1812F184K1RACT U]	180 pF [C0402C181K5RACT U]
180 nF [C0805C184K3RACT U]	180 nF [C1210C184K1RACT U]	180 nF [C1812F184K2RACT U]	180 pF [C0402C181K8RACT U]
180 nF [C0805C184K4RACT U]	180 nF [C1210C184K3HACT U]	180 nF [C1812F184K3RACT U]	180 pF [C0603C181K1RACT U]
180 nF [C0805C184K5RACT U]	180 nF [C1210C184K5RACT U]	180 nF [C1812F184K5RACT U]	180 pF [C0603C181K2RACT U]
180 nF [C0805C184K8RACT U]	180 nF [C1210F184K1RACT U]	180 nF [C1825C184K5RACT U]	180 pF [C0603C181K3RACT U]
180 nF [C1206C184K1RACT U]	180 nF [C1210F184K3RACT U]	180 nF [C2225C184K1RACT U]	180 pF [C0603C181K4RACT U]
180 nF [C1206C184K5RACT U]	180 nF [C1210F184K4RACT U]	180 pF [C0402C181K1HACT U]	180 pF [C0603C181K5GACT U]
180 nF [C1206C184M5UAC TU]	180 nF [C1210F184K5RACT U]	180 pF [C0402C181K3HACT U]	180 pF [C0603C181K5RACT U]

# Multisim 14.0 Education Components

---

180 pF [C0603C181K8RACT U]	180 pF [C2220C181KBGAC TU]	180 uF [A700X187M006AT E010]	183-015-113R161  183-015-213R161
180 pF [C0805C181K1GACT U]	180 pF [C2225C181KBGAC TU]	180 uF [A700X187M006AT E015]	183-025-113R161  183-025-213R161
180 pF [C0805C181K2GACT U]	180 pF [CA064C181K4GAC TU]	181-015-113R431  181-015-213R431	183-037-113R161  183-037-213R161
180 pF [C0805C181K5GACT U]	180 pF [CA064C181K5GAC TU]	181-026-113R431  181-026-213R431	18TQ045  1932258-1
180 pF [C1206C181K1GACT U]	180 uF [A700D187M002AT E015]	181-044-113R431  181-044-213R431	1981584-1  1B4B42
180 pF [C1206C181K2GACT U]	180 uF [A700D187M002AT E018]	181-062-113R431  181-062-213R431	1BH62  1DH62
180 pF [C1206C181K5GACT U]	180 uF [A700D187M004AT E015]	181-078-113R431  181-078-213R431	1G4B42  1GH62
180 pF [C1206C181KBGAC TU]	180 uF [A700D187M004AT E018]	182-009-113R431  182-009-213R431	1J4B42  1JH62
180 pF [C1210C181KBGAC TU]	180 uF [A700D187M2R5AT E015]	182-015-113R431  182-015-213R431	1L2.5SP  1L5SP
180 pF [C1812C181KBGAC TU]	180 uF [A700D187M2R5AT E018]	182-025-113R431  182-025-213R431	1LH62  1N1199C
180 pF [C1825C181KBGAC TU]	180 uF [A700X187M004AT E010]	182-037-113R431  182-037-213R431	1N1200C  1N1202C
		183-009-113R161  183-009-213R161	1N1204C  1N1206C
			1N3064

# Multisim 14.0 Education Components

---

1N3208	1N3881A	1N3957GP	1N4009
1N3491	1N3882	1N4001G	1N4148
1N3492	1N3882A	1N4001GP	1N4149
1N3493	1N3883	1N4001RLG	1N4150
1N3494	1N3883A	1N4002G	1N4151
1N3495	1N3889	1N4002GP	1N4152
1N3611GP	1N3889A	1N4002RLG	1N4153
1N3612GP	1N3890	1N4003G	1N4154
1N3613GP	1N3890A	1N4003GP	1N4245GP
1N3614GP	1N3891	1N4003RLG	1N4246GP
1N3659	1N3891A	1N4004G	1N4247GP
1N3660	1N3892	1N4004GP	1N4248GP
1N3661	1N3892A	1N4004RLG	1N4249GP
1N3662	1N3893	1N4005G	1N4305
1N3663	1N3893A	1N4005GP	1N4370A
1N3712	1N3899	1N4005RLG	1N4371A
1N3713	1N3900	1N4006FFG	1N4372A
1N3714	1N3901	1N4006G	1N4383GP
1N3715	1N3902	1N4006GP	1N4384GP
1N3720	1N3903	1N4006RLG	1N4385GP
1N3879	1N3909	1N4007-E3/54	1N4446
1N3879A	1N3910	1N4007FFG	1N4447
1N3880	1N3911	1N4007G	1N4448
1N3880A	1N3912	1N4007GP	1N4449
1N3881	1N3913	1N4007RLG	1N4454

# Multisim 14.0 Education Components

---

1N4585GP	1N4749A	1N4936	1N5230B
1N4586GP	1N4750A	1N4936G	1N5231B
1N4678	1N4751A	1N4936RLG	1N5232B
1N4681	1N4752A	1N4937	1N5233B
1N4728A	1N4753A	1N4937G	1N5234B
1N4729A	1N4754A	1N4937RLG	1N5235B
1N4730A	1N4755A	1N4938	1N5236B
1N4731A	1N4756A	1N4942GP	1N5237B
1N4732A	1N4757A	1N4944GP	1N5238B
1N4733A	1N4758A	1N4946GP	1N5239B
1N4734A	1N4759A	1N4947GP	1N5240B
1N4735A	1N4760A	1N4948GP	1N5241B
1N4736A	1N4761A	1N5059GP	1N5242B
1N4737A	1N4762A	1N5060GP	1N5243B
1N4738A	1N4763A	1N5061GP	1N5244B
1N4739A	1N4764A	1N5062GP	1N5245B
1N4740A	1N4933	1N5221B	1N5246B
1N4741A	1N4933G	1N5222B	1N5247B
1N4742A	1N4933RLG	1N5223B	1N5248B
1N4743A	1N4934	1N5224B	1N5249B
1N4744A	1N4934G	1N5225B	1N5250B
1N4745A	1N4934RLG	1N5226B	1N5251B
1N4746A	1N4935	1N5227B	1N5252B
1N4747A	1N4935G	1N5228B	1N5253B
1N4748A	1N4935RLG	1N5229B	1N5254B

# Multisim 14.0 Education Components

---

1N5255B	1N5280B	1N5346BG	1N5361BG
1N5256B	1N5281B	1N5346BRLG	1N5361BRLG
1N5257B	1N5333BRLG	1N5347BG	1N5362BG
1N5258B	1N5334BRLG	1N5347BRLG	1N5362BRLG
1N5259B	1N5335BG	1N5348BG	1N5363BG
1N5260B	1N5335BRLG	1N5348BRLG	1N5363BRLG
1N5261B	1N5336BG	1N5349BG	1N5364BG
1N5262B	1N5336BRLG	1N5349BRLG	1N5364BRLG
1N5263B	1N5337BG	1N5350BG	1N5365BG
1N5264B	1N5337BRLG	1N5350BRLG	1N5365BRLG
1N5265B	1N5338BG	1N5351BG	1N5366BG
1N5266B	1N5338BRLG	1N5351BRLG	1N5366BRLG
1N5267B	1N5339BG	1N5352BG	1N5367BG
1N5268B	1N5339BRLG	1N5352BRLG	1N5367BRLG
1N5269B	1N5340BG	1N5353BG	1N5368BG
1N5270B	1N5340BRLG	1N5353BRLG	1N5368BRLG
1N5271B	1N5341BG	1N5355BG	1N5369BG
1N5272B	1N5341BRLG	1N5355BRLG	1N5369BRLG
1N5273B	1N5342BG	1N5356BRLG	1N5371BRLG
1N5274B	1N5342BRLG	1N5357BG	1N5372BG
1N5275B	1N5343BG	1N5357BRLG	1N5372BRLG
1N5276B	1N5343BRLG	1N5358BG	1N5373BG
1N5277B	1N5344BG	1N5358BRLG	1N5373BRLG
1N5278B	1N5344BRLG	1N5359BG	1N5374BG
1N5279B	1N5345BRLG	1N5359BRLG	1N5374BRLG



# Multisim 14.0 Education Components

---

1N5375BG	1N5400RLG	1N5759	1N5826
1N5375BRLG	1N5401	1N5759A	1N5827
1N5378BG	1N5401G	1N5760	1N5828
1N5378BRLG	1N5401RLG	1N5761	1N5829
1N5381BRLG	1N5402	1N5761A	1N5830
1N5383BG	1N5402G	1N5817-E3/54	1N5831
1N5383BRLG	1N5402RLG	1N5817G	1N5832
1N5384BG	1N5404	1N5817RLG	1N5833
1N5384BRLG	1N5404G	1N5818G	1N5834
1N5386BG	1N5404RLG	1N5818RLG	1N5913B
1N5386BRLG	1N5406	1N5819G	1N5913BRLG
1N5388BG	1N5406G	1N5819RLG	1N5914B
1N5388BRLG	1N5406RLG	1N5820	1N5915B
1N5391	1N5407G	1N5820G	1N5916B
1N5391GP	1N5407RLG	1N5820RLG	1N5917B
1N5392GP	1N5408-E3/54	1N5821	1N5918B
1N5393GP	1N5408G	1N5821G	1N5919B
1N5394GP	1N5408RLG	1N5821RLG	1N5919BG
1N5395GP	1N5615GP	1N5822	1N5919BRLG
1N5396GP	1N5617GP	1N5822-E3/54	1N5920B
1N5397GP	1N5619GP	1N5822G	1N5920BG
1N5398GP	1N5621GP	1N5822RLG	1N5921B
1N5399GP	1N5623GP	1N5823	1N5921BG
1N5400	1N5758	1N5824	1N5921BRLG
1N5400G	1N5758A	1N5825	1N5922B

# Multisim 14.0 Education Components

---

1N5923B	1N5936B	1N5986B	1N6011B
1N5923BRLG	1N5937B	1N5987B	1N6012B
1N5924B	1N5937BRLG	1N5988B	1N6013B
1N5924BRLG	1N5938B	1N5989B	1N6014B
1N5925B	1N5938BRLG	1N5990B	1N6015B
1N5925BRLG	1N5939B	1N5991B	1N6016B
1N5926B	1N5940B	1N5992B	1N6017B
1N5927B	1N5940BRLG	1N5993B	1N6018B
1N5927BG	1N5941B	1N5994B	1N6019B
1N5927BRLG	1N5941BRLG	1N5995B	1N6020B
1N5928B	1N5942B	1N5996B	1N6021B
1N5929B	1N5942BRLG	1N5997B	1N6022B
1N5929BG	1N5943B	1N5998B	1N6023B
1N5929BRLG	1N5944B	1N5999B	1N6024B
1N5930B	1N5945B	1N6000B	1N6025B
1N5931B	1N5946B	1N6001B	1N6096
1N5931BRLG	1N5946BRLG	1N6002B	1N6098
1N5932B	1N5947B	1N6003B	1N6285AG
1N5932BRLG	1N5948BRLG	1N6004B	1N6285ARL4G
1N5933B	1N5953BG	1N6005B	1N6287AG
1N5934B	1N5953BRLG	1N6006B	1N6287ARL4G
1N5934BG	1N5955BRLG	1N6007B	1N6292AG
1N5934BRLG	1N5956BG	1N6008B	1N6292ARL4G
1N5935B	1N5956BRLG	1N6009B	1N6294ARL4G
1N5935BRLG	1N5985B	1N6010B	1N6373-E3/51

# Multisim 14.0 Education Components

---

1N6478	1N916B	1N981B	1PS302
1N6479	1N957B	1N982B	1PS66SB17
1N6480	1N958B	1N983B	1PS66SB82
1N6481	1N959B	1N984B	1PS70SB10
1N6482	1N960B	1N985B	1PS70SB14
1N6483	1N961B	1N986B	1PS70SB15
1N6484	1N962B	1N987B	1PS70SB16
1N747A	1N963B	1N988B	1PS70SB20
1N748A	1N964B	1N989B	1PS70SB40
1N749A	1N965B	1N990B	1PS70SB44
1N750A	1N966B	1N991B	1PS70SB45
1N751A	1N967B	1N992B	1PS70SB46
1N752A	1N968B	1P1S	1PS70SB82
1N753A	1N969B	1P2S	1PS70SB84
1N754A	1N970B	1P3S	1PS70SB85
1N755A	1N971B	1P4S	1PS70SB86
1N756A	1N972B	1P5S	1PS74SB23
1N757A	1N973B	1PMT12AT1G	1PS75SB45
1N758A	1N974B	1PMT16AT3G	1PS76SB10
1N759A	1N975B	1PMT33AT3G	1PS76SB17
1N914	1N976B	1PMT5.0AT1G	1PS76SB40
1N914A	1N977B	1PMT5927BT1G	1PS76SB70
1N914B	1N978B	1PS10SB82	1PS79SB10
1N916	1N979B	1PS300	1PS79SB17
1N916A	1N980B	1PS301	1PS79SB30

# Multisim 14.0 Education Components

---

1PS79SB31	1SMA5922BT3G	1SMB5918BT3G	1Z13
1PS79SB40	1SMA5927BT3G	1SMB5919BT3G	1Z14
1PS79SB70	1SMA5931BT3G	1SMB5920BT3G	1Z15
1PS88SB48	1SMA5932BT3G	1SMB5921BT3G	1Z30
1PS88SB82	1SMA5936BT3G	1SMB5922BT3G	1Z6.2
1S1553	1SMA5940BT3G	1SMB5924BT3G	1Z6.8
1S1554	1SMB12AT3G	1SMB5925BT3G	1Z7.5
1S1555	1SMB14AT3G	1SMB5927BT3G	1Z8.2
1S1830	1SMB170AT3G	1SMB5930BT3G	1Z9.1
1S1834	1SMB18CAT3G	1SMB5931BT3G	1ZB10
1S1835	1SMB20CAT3G	1SMB5933BT3G	1ZB11
1S1885	1SMB22CAT3G	1SMB5934BT3G	1ZB12
1S1887	1SMB24AT3G	1SMB5935BT3G	1ZB13
1S1888	1SMB24CAT3G	1SMB5936BT3G	1ZB14
1S953	1SMB26CAT3G	1SMB5937BT3G	1ZB15
1S954	1SMB28AT3G	1SMB5939BT3G	1ZB30
1S955	1SMB28CAT3G	1SMB5940BT3G	1ZB6.8
1SMA12CAT3G	1SMB30AT3G	1SMB70AT3G	1ZB7.5
1SMA26AT3G	1SMB30CAT3G	1SMB85AT3G	1ZB8.2
1SMA30AT3G	1SMB33CAT3G	1SMC28AT3G	1ZB9.1
1SMA40CAT3G	1SMB36CAT3G	1SMC36AT3G	2 nF
1SMA5.0AT3G	1SMB5.0AT3G	1SMC6.0AT3G	[C0603C202K1HACT U]
1SMA5913BT3G	1SMB54CAT3G	1Z10	2 nF
1SMA5918BT3G	1SMB58CAT3G	1Z11	[C0603C202K3HACT U]
1SMA5921BT3G	1SMB5914BT3G	1Z12	

# Multisim 14.0 Education Components

---

2 nF [C0603C202K5HACT U]	2.2 nF [C0603C222K1RACT U]	2.2 nF [C0805C222K1HACT U]	2.2 nF [C1206C222K2RACT U]
2 nF [C1210C202KCGAC TU]	2.2 nF [C0603C222K2RACT U]	2.2 nF [C0805C222K1RACT U]	2.2 nF [C1206C222K4RACT U]
2 nF [C1812C202KBGAC TU]	2.2 nF [C0603C222K3GACT U]	2.2 nF [C0805C222K2RACT U]	2.2 nF [C1206C222K5GACT U]
2 nF [C1825C202KBGAC TU]	2.2 nF [C0603C222K3HACT U]	2.2 nF [C0805C222K3GACT U]	2.2 nF [C1206C222K5RACT U]
2 nF [C2220C202KBGAC TU]	2.2 nF [C0603C222K3RACT U]	2.2 nF [C0805C222K3HACT U]	2.2 nF [C1210C222K1GACT U]
2 nF [C2225C202KBGAC TU]	2.2 nF [C0603C222K4RACT U]	2.2 nF [C0805C222K3RACT U]	2.2 nF [C1210C222K1RACT U]
2.2 nF [C0402C222K3RACT U]	2.2 nF [C0603C222K5HACT U]	2.2 nF [C0805C222K5HACT U]	2.2 nF [C1210C222K2GACT U]
2.2 nF [C0402C222K4RACT U]	2.2 nF [C0603C222K5RACT U]	2.2 nF [C0805C222K5RACT U]	2.2 nF [C1210C222K5GACT U]
2.2 nF [C0402C222K5RACT U]	2.2 nF [C0603C222K8RACT U]	2.2 nF [C0805C222KARACT U]	2.2 nF [C1210C222KCGAC TU]
2.2 nF [C0402C222K8RACT U]	2.2 nF [C0603C222K9RACT U]	2.2 nF [C1206C222K1GACT U]	2.2 nF [C1812C222K2GACT U]
2.2 nF [C0603C222K1HACT U]	2.2 nF [C0805C222K1GACT U]	2.2 nF [C1206C222K1RACT U]	2.2 nF [C1812C222KBGAC TU]

# Multisim 14.0 Education Components

---

2.2 nF [C1812C222KDGAC TU]	2.2 uF [C0805C225K4PACT U]	2.2 uF [C1206C225K4RACT U]	2.2 uF [C1210C225K8RACT U]
2.2 nF [C1825C222KBGAC TU]	2.2 uF [C0805C225K4RACT U]	2.2 uF [C1206C225K8PACT U]	2.2 uF [C1210C225K9PACT U]
2.2 nF [C2220C222KBGAC TU]	2.2 uF [C0805C225K8PACT U]	2.2 uF [C1206C225K8RACT U]	2.2 uF [C1210C225K9RACT U]
2.2 nF [C2225C222KBGAC TU]	2.2 uF [C0805C225K8RACT U]	2.2 uF [C1206C225K9PACT U]	2.2 uF [C1210C225M8VAC TU]
2.2 nF [CA064C222K1RACT U]	2.2 uF [C0805C225K9PACT U]	2.2 uF [C1206C225K9RACT U]	2.2 uF [C1812C225K1RACT U]
2.2 nF [CA064C222K4RACT U]	2.2 uF [C0805C225K9RACT U]	2.2 uF [C1206C225M4VAC TU]	2.2 uF [C1825C225K5RACT U]
2.2 nF [CA064C222K5RACT U]	2.2 uF [C0805C225M4VAC TU]	2.2 uF [C1210C225K1RACT U]	2.2 uF [C2220C225K5RACT U]
2.2 uF [C0402C225K9PACT U]	2.2 uF [C0805C225M8VAC TU]	2.2 uF [C1210C225K3PACT U]	2.2 uF [C2225C225K5RACT U]
2.2 uF [C0603C225K4PACT U]	2.2 uF [C1206C225K3NAC TU]	2.2 uF [C1210C225K3RACT U]	2.2 uF [C2225C225M5UAC TU]
2.2 uF [C0603C225K8PACT U]	2.2 uF [C1206C225K3PACT U]	2.2 uF [C1210C225K4RACT U]	2.2 uF [T409C225M015AH 4250]
2.2 uF [C0603C225K9PACT U]	2.2 uF [C1206C225K4PACT U]	2.2 uF [C1210C225K5RACT U]	2.2 uF [T429A225M010AH 4250]

# Multisim 14.0 Education Components

---

2.2 uF [T429C225M015AH 4250]	2.2 uF [T494A225M006AT]	2.4 nF [C0603C242K1HACT U]	2.7 nF [C0402C272K4RACT U]
2.2 uF [T491A225M006AT]	2.2 uF [T494A225M010AT]	2.4 nF [C0603C242K3HACT U]	2.7 nF [C0402C272K5RACT U]
2.2 uF [T491A225M010AT]	2.2 uF [T494A225M016AT]	2.4 nF [C0603C242K5HACT U]	2.7 nF [C0603C272K1HACT U]
2.2 uF [T491A225M016AT]	2.2 uF [T494A225M020AT]	2.4 nF [C0805C242K1GACT U]	2.7 nF [C0603C272K1RACT U]
2.2 uF [T491A225M020AT]	2.2 uF [T494B225M025AT]	2.4 nF [C0805C242K1HACT U]	2.7 nF [C0603C272K3GACT U]
2.2 uF [T491A225M025AT]	2.2 uF [T494B225M035AT]	2.4 nF [C0805C242K3HACT U]	2.7 nF [C0603C272K3HACT U]
2.2 uF [T491B225M010AT]	2.2 uF [T494C225M025AT]	2.4 nF [C0805C242K5HACT U]	2.7 nF [C0603C272K3RACT U]
2.2 uF [T491B225M020AT]	2.2 uF [T494C225M035AT]	2.4 nF [C1825C242KBGAC TU]	2.7 nF [C0603C272K4RACT U]
2.2 uF [T491B225M025AT]	2.2 uF [T494D225M050AT ]	2.4 nF [C2220C242KBGAC TU]	2.7 nF [C0603C272K5HACT U]
2.2 uF [T491B225M035AT]	2.2 uF [T494S225M016AT]	2.4 nF [C2225C242KBGAC TU]	2.7 nF [C0603C272K5RACT U]
2.2 uF [T491C225M035AT]	2.2 uF [T498A225M010AT E4K6]	2.7 nF [C0402C272K3RACT U]	2.7 nF [C0603C272K8RACT U]
2.2 uF [T491D225M050AT ]	2.2 uF [T498B225M025AT E3K0]		
2.2 uF [T491S225M016AT]			

# Multisim 14.0 Education Components

---

2.7 nF [C0805C272K1GACT U]	2.7 nF [C0805C272KARACT U]	2.7 nF [C1825C272KBGAC TU]	20 pF [C0402C200K8GACT U]
2.7 nF [C0805C272K1HACT U]	2.7 nF [C1206C272K1GACT U]	2.7 nF [C2220C272KBGAC TU]	20 pF [C0603C200K2GACT U]
2.7 nF [C0805C272K1RACT U]	2.7 nF [C1206C272K1RACT U]	2.7 nF [C2225C272KBGAC TU]	20 pF [C0603C200K4GACT U]
2.7 nF [C0805C272K2RACT U]	2.7 nF [C1206C272K2RACT U]	2.7 uF [C0805C275K8PACT U]	20 pF [C0603C200K5GACT U]
2.7 nF [C0805C272K3GACT U]	2.7 nF [C1206C272K5GACT U]	2.7 uF [C1206C275K3PACT U]	20 pF [C0805C200K1GACT U]
2.7 nF [C0805C272K3HACT U]	2.7 nF [C1206C272K5RACT U]	2.7 uF [C1206C275K4PACT U]	20 pF [C0805C200K2GACT U]
2.7 nF [C0805C272K3RACT U]	2.7 nF [C1210C272K2GACT U]	2.7 uF [C1206C275K4RACT U]	20 pF [C0805C200K5GACT U]
2.7 nF [C0805C272K4GACT U]	2.7 nF [C1210C272K5GACT U]	2.7 uF [C1206C275K8RACT U]	20 pF [C0805C200KBGAC TU]
2.7 nF [C0805C272K4RACT U]	2.7 nF [C1210C272KCGAC TU]	2.7 uF [C1206C275K9PACT U]	20 pF [C1206C200K1GACT U]
2.7 nF [C0805C272K5HACT U]	2.7 nF [C1812C272K1GACT U]	2.7 uF [C1206C275K9RACT U]	20 pF [C1206C200K5GACT U]
2.7 nF [C0805C272K5RACT U]	2.7 nF [C1812C272K5GACT U]	2 AMP 20 pF [C0402C200K5GACT U]	20 pF [C1206C200KBGAC TU]



# Multisim 14.0 Education Components

---

20 pF [C1206C200KCGAC TU]	200 pF [C0805C201K5GACT U]	22 nF [C0402C223K5RACT U]	22 nF [C0603C223M8VAC TU]
20 pF [C1210C200KBGAC TU]	200 pF [C1206C201K5GACT U]	22 nF [C0402C223K8PACT U]	22 nF [C0805C223K1RACT U]
20 pF [C1812C200KBGAC TU]	200 pF [C1206C201KBGAC TU]	22 nF [C0402C223K8RACT U]	22 nF [C0805C223K2RACT U]
20 pF [C1825C200KBGAC TU]	200 pF [C1210C201KBGAC TU]	22 nF [C0402C223K9PACT U]	22 nF [C0805C223K3GACT U]
20 pF [C2220C200KBGAC TU]	200 pF [C1812C201KBGAC TU]	22 nF [C0402C223K9RACT U]	22 nF [C0805C223K3HACT U]
20 pF [C2225C200KBGAC TU]	200 pF [C2220C201KBGAC TU]	22 nF [C0603C223K1RACT U]	22 nF [C0805C223K3RACT U]
20_AMP  200 pF [C0402C201K1HACT U]	200 pF [C2225C201KBGAC TU]  2013655-1  20CJQ030  20CLQ045  20ETS12	22 nF [C0603C223K3RACT U]  22 nF [C0603C223K4RACT U]  22 nF [C0603C223K5RACT U]	22 nF [C0805C223K4RACT U]  22 nF [C0805C223K5HACT U]  22 nF [C0805C223K5RACT U]
200 pF [C0402C201K3HACT U]	22 nF [C0402C223K3RACT U]	22 nF [C0603C223K8RACT U]	22 nF [C0805C223K8RACT U]
200 pF [C0603C201K5GACT U]	22 nF [C0402C223K4RACT U]	22 nF [C0603C223M3VAC TU]	22 nF [C0805C223KARACT U]
200 pF [C0805C201K2GACT U]			

# Multisim 14.0 Education Components

---

22 nF [C0805C223M5UAC TU]	22 nF [C1206C223K4RACT U]	22 nF [C1210C223K5GACT U]	22 nF [C1825C223K1GACT U]
22 nF [C0805F223K1RACT U]	22 nF [C1206C223K5HACT U]	22 nF [C1210C223K5HACT U]	22 nF [C1825C223K5GACT U]
22 nF [C0805F223K3RACT U]	22 nF [C1206C223K5RACT U]	22 nF [C1210C223K5RACT U]	22 nF [C1825C223K5RACT U]
22 nF [C0805F223K4RACT U]	22 nF [C1206C223M5UAC TU]	22 nF [C1210C223KARACT U]	22 nF [C2220C223K1GACT U]
22 nF [C0805F223K5RACT U]	22 nF [C1206F223K2RACT U]	22 nF [C1812C223K1GACT U]	22 nF [C2220C223K2GACT U]
22 nF [C1206C223K1HACT U]	22 nF [C1210C223K1GACT U]	22 nF [C1812C223K1HACT U]	22 nF [C2225C223K1GACT U]
22 nF [C1206C223K1RACT U]	22 nF [C1210C223K1HACT U]	22 nF [C1812C223K1RACT U]	22 nF [C2225C223K5GACT U]
22 nF [C1206C223K2RACT U]	22 nF [C1210C223K1RACT U]	22 nF [C1812C223K2RACT U]	22 pF [C0201C220K3GACT U]
22 nF [C1206C223K3GACT U]	22 nF [C1210C223K2RACT U]	22 nF [C1812C223K5GACT U]	22 pF [C0402C220K3GACT U]
22 nF [C1206C223K3HACT U]	22 nF [C1210C223K3GACT U]	22 nF [C1812C223K5HACT U]	22 pF [C0402C220K4GACT U]
22 nF [C1206C223K3RACT U]	22 nF [C1210C223K3HACT U]	22 nF [C1812C223K5RACT U]	22 pF [C0402C220K5GACT U]

# Multisim 14.0 Education Components

---

22 pF [C0402C220K8GACT U]	22 pF [C0805C220KCGAC TU]	22 pF [C1812C220KBGAC TU]	22 uF [A700V226M006AT E045]
22 pF [C0603C220K1GACT U]	22 pF [C0805C220KDGAC TU]	22 pF [C1825C220KBGAC TU]	22 uF [A700V226M008AT E028]
22 pF [C0603C220K2GACT U]	22 pF [C1206C220K1GACT U]	22 pF [C2220C220KBGAC TU]	22 uF [A700V226M008AT E045]
22 pF [C0603C220K3GACT U]	22 pF [C1206C220K2GACT U]	22 pF [C2225C220KBGAC TU]	22 uF [A700V226M010AT E028]
22 pF [C0603C220K4GACT U]	22 pF [C1206C220K5GACT U]	22 pF [CA064C220K2GAC TU]	22 uF [A700V226M12RAT E030]
22 pF [C0603C220K5GACT U]	22 pF [C1206C220KBGAC TU]	22 pF [CA064C220K3GAC TU]	22 uF [C0805C226K9PACT U]
22 pF [C0805C220K1GACT U]	22 pF [C1206C220KCGAC TU]	22 pF [CA064C220K4GAC TU]	22 uF [C1206C226K9PACT U]
22 pF [C0805C220K2GACT U]	22 pF [C1206C220KDGAC TU]	22 pF [CA064C220K5GAC TU]	22 uF [C1206C226M9VAC TU]
22 pF [C0805C220K3GACT U]	22 pF [C1210C220K2GACT U]	22 pF [CA064C220K8GAC TU]	22 uF [C1210C226K4PACT U]
22 pF [C0805C220K5GACT U]	22 pF [C1210C220K5GACT U]	22 uF [A700D226M016AT E018]	22 uF [C1210C226K8PACT U]
22 pF [C0805C220KBGAC TU]	22 pF [C1210C220KBGAC TU]	22 uF [A700V226M006AT E028]	22 uF [C1210C226K8RACT U]

# Multisim 14.0 Education Components

---

22 uF [C1210C226K9PACT U]	22 uF [T491C226M004AT]	22 uF [T491T226M006AT]	22 uF [T494B226M006AT]
22 uF [C1210C226K9RACT U]	22 uF [T491C226M006AT]	22 uF [T491T226M010AT]	22 uF [T494B226M010AT]
22 uF [C1210C226M8VAC TU]	22 uF [T491C226M010AT]	22 uF [T491U226M006AT ]	22 uF [T494B226M016AT]
22 uF [T419G226M020AH 4250]	22 uF [T491C226M016AT]	22 uF [T491U226M010AT ]	22 uF [T494B226M020AT]
22 uF [T429D226M006AH 4250]	22 uF [T491C226M020AT]	22 uF [T491U226M016AT ]	22 uF [T494C226M004AT]
22 uF [T491A226M004AT]	22 uF [T491C226M025AT]	22 uF [T491V226M020AT]	22 uF [T494C226M006AT]
22 uF [T491A226M006AT]	22 uF [T491D226M010AT ]	22 uF [T491V226M025AT]	22 uF [T494C226M010AT]
22 uF [T491A226M010AT]	22 uF [T491D226M016AT ]	22 uF [T491X226M035AT]	22 uF [T494C226M016AT]
22 uF [T491B226M004AT]	22 uF [T491D226M020AT ]	22 uF [T491X226M050AT]	22 uF [T494C226M020AT]
22 uF [T491B226M006AT]	22 uF [T491D226M025AT ]	22 uF [T493X226M025AH 6110]	22 uF [T494C226M025AT]
22 uF [T491B226M010AT]	22 uF [T491D226M035AT ]	22 uF [T494A226M025AH 6110]	22 uF [T494D226M010AT ]
22 uF [T491B226M016AT]	22 uF [T491S226M004AT]	22 uF [T494A226M004AT]	22 uF [T494D226M016AT ]
22 uF [T491B226M020AT]	22 uF [T491T226M004AT]	22 uF [T494A226M006AT]	22 uF [T494D226M020AT ]
		22 uF [T494A226M010AT]	22 uF [T494D226M025AT ]
		22 uF [T494B226M004AT]	

# Multisim 14.0 Education Components

---

22 uF [T494D226M035AT ]	22 uF [T495C226M025AT E900]	22 uF [T497D226M006AT 6110]	22 uF [T520A226M006AT E090]
22 uF [T494S226M004AT]	22 uF [T495D226M020AT E180]	22 uF [T498B226M010AT E1K5]	22 uF [T520A226M006AT E100]
22 uF [T494T226M004AT]	22 uF [T495D226M020AT E225]	22 uF [T498C226M006AT E1K3]	22 uF [T520A226M010AT E080]
22 uF [T494T226M006AT]	22 uF [T495D226M025AT E200]	22 uF [T498C226M010AT E1K1]	22 uF [T520C226M016AT E080]
22 uF [T494U226M006AT ]	22 uF [T495D226M035AT E125]	22 uF [T498C226M016AT E1K0]	22 uF [T520T226M008AT E070]
22 uF [T494U226M010AT ]	22 uF [T495D226M035AT E200]	22 uF [T498D226M025AT E600]	22 uF [T520V226M020AT E045]
22 uF [T494U226M016AT ]	22 uF [T495D226M035AT E300]	22 uF [T498X226M035AT E500]	22 uF [T520V226M020AT E090]
22 uF [T494V226M020AT]	22 uF [T495X226M025AT E225]	22 uF [T499D226M016AT E800]	22 uF [T521V226M025AT E060]
22 uF [T494V226M025AT]	22 uF [T495X226M035AT E125]	22 uF [T510X226M035AT E060]	22 uF [T525B226M010AT E080]
22 uF [T494X226M035AT]	22 uF [T495X226M035AT E200]	22 uF [T510X226M035AT E080]	22 uF [T541X226M050AH 6510]
22 uF [T495C226M025AT E300]	22 uF [T495X226M035AT E275]	22 uF [T510X226M035AT E100]	220 nF [C0402C224K9PACT U]

# Multisim 14.0 Education Components

---

220 nF [C0603C224K3RACT U]	220 nF [C0805C224K8RACT U]	220 nF [C1210C224K1RACT U]	220 nF [C1812C224K5RACT U]
220 nF [C0603C224K4RACT U]	220 nF [C0805C224M3VAC TU]	220 nF [C1210C224K3GACT U]	220 nF [C1812C224KARACT U]
220 nF [C0603C224K8NAC TU]	220 nF [C0805C224M4VAC TU]	220 nF [C1210C224K3RACT U]	220 nF [C1812C224M5UAC TU]
220 nF [C0603C224K8RACT U]	220 nF [C1206C224K1RACT U]	220 nF [C1210C224K5RACT U]	220 nF [C1812F224K1RACT U]
220 nF [C0603C224K9RACT U]	220 nF [C1206C224K3RACT U]	220 nF [C1210C224M5UAC TU]	220 nF [C1812F224K2RACT U]
220 nF [C0603C224M3VAC TU]	220 nF [C1206C224K4RACT U]	220 nF [C1210F224K1RACT U]	220 nF [C1812F224K3RACT U]
220 nF [C0603C224M4VAC TU]	220 nF [C1206C224K5RACT U]	220 nF [C1210F224K3RACT U]	220 nF [C1812F224K5RACT U]
220 nF [C0603C224M8VAC TU]	220 nF [C1206C224M5UAC TU]	220 nF [C1210F224K4RACT U]	220 nF [C1825C224K1RACT U]
220 nF [C0805C224K3RACT U]	220 nF [C1206F224K3RACT U]	220 nF [C1210F224K5RACT U]	220 nF [C1825C224K2RACT U]
220 nF [C0805C224K4RACT U]	220 nF [C1206F224K4RACT U]	220 nF [C1812C224K1RACT U]	220 nF [C1825C224K5RACT U]
220 nF [C0805C224K5RACT U]	220 nF [C1206F224K5RACT U]	220 nF [C1812C224K5HACT U]	220 nF [C1825C224M1UAC TU]

# Multisim 14.0 Education Components

---

220 nF [C1825C224M5UAC TU]	220 pF [C0402C221K1HACT U]	220 pF [C0603C221K3RACT U]	220 pF [C0805C221K3RACT U]
220 nF [C2220C224K1GACT U]	220 pF [C0402C221K3HACT U]	220 pF [C0603C221K4GACT U]	220 pF [C0805C221K4RACT U]
220 nF [C2220C224K5GACT U]	220 pF [C0402C221K3RACT U]	220 pF [C0603C221K4RACT U]	220 pF [C0805C221K5GACT U]
220 nF [C2225C224K1RACT U]	220 pF [C0402C221K4RACT U]	220 pF [C0603C221K5GACT U]	220 pF [C0805C221K5RACT U]
220 nF [C2225C224K5RACT U]	220 pF [C0402C221K5GACT U]	220 pF [C0603C221K5RACT U]	220 pF [C0805C221K8RACT U]
220 nF [T409A224M035AH 4250]	220 pF [C0402C221K5HACT U]	220 pF [C0603C221K8RACT U]	220 pF [C0805C221KARACT U]
220 nF [T491A224M035AT]	220 pF [C0402C221K5RACT U]	220 pF [C0805C221K1GACT U]	220 pF [C1206C221K1GACT U]
220 nF [T491B224M050AT]	220 pF [C0402C221K8RACT U]	220 pF [C0805C221K1RACT U]	220 pF [C1206C221K2GACT U]
220 nF [T493B224M050AH 6120]	220 pF [C0603C221K1RACT U]	220 pF [C0805C221K2GACT U]	220 pF [C1206C221K5GACT U]
220 nF [T494A224M035AT]	220 pF [C0603C221K2RACT U]	220 pF [C0805C221K2RACT U]	220 pF [C1206C221KBGAC TU]
220 nF [T499A224M035AT E18K]	220 pF [C0603C221K3GACT U]	220 pF [C0805C221K3GACT U]	220 pF [C1206C221KCGAC TU]

# Multisim 14.0 Education Components

---

220 pF [C1206C221KDGAC TU]	220 uF [A700D227M004AT E009]	220 uF [T491E227M016AT]	220 uF [T494X227M006AT]
220 pF [C1210C221K1GACT U]	220 uF [A700V227M002AT E009]	220 uF [T491V227M004AT]	220 uF [T494X227M010AT]
220 pF [C1210C221KBGAC TU]	220 uF [A700X227M004AT E010]	220 uF [T491X227M006AT]	220 uF [T495C227M006AT E225]
220 pF [C1812C221KBGAC TU]	220 uF [A700X227M004AT E015]	220 uF [T491X227M010AT]	220 uF [T495D227M004AT E040]
220 pF [C1825C221KBGAC TU]	220 uF [A700X227M2R5AT E010]	220 uF [T491X227M016AT]	220 uF [T495D227M004AT E050]
220 pF [C2220C221KBGAC TU]	220 uF [A700X227M2R5AT E015]	220 uF [T494C227M006AT]	220 uF [T495D227M004AT E100]
220 pF [C2225C221KBGAC TU]	220 uF [T419H227M004AH 4250]	220 uF [T494D227M006AT ]	220 uF [T495D227M006AT E045]
220 pF [CA064C221K5GAC TU]	220 uF [T491B227M004AT]	220 uF [T494D227M010AT ]	220 uF [T495D227M006AT E100]
220 pF [CDR02BP221BKSM ]	220 uF [T491C227M006AT]	220 uF [T494D227M2R5AT ]	220 uF [T495D227M010AT E045]
220 uF [A700D227M002AT E015]	220 uF [T491D227M006AT ]	220 uF [T494E227M016AT]	220 uF [T495D227M010AT E075]
220 uF [A700D227M002AT E018]	220 uF [T491D227M010AT ]	220 uF [T494V227M004AT]	220 uF [T495D227M010AT E100]
	220 uF [T491D227M2R5AT ]		



# Multisim 14.0 Education Components

---

220 uF [T495D227M010AT E125]	220 uF [T495X227M016AT E100]	220 uF [T520B227M2R5AT E015]	220 uF [T520C227M006AT E045]
220 uF [T495D227M2R5AT E045]	220 uF [T496X227M010AT 6110]	220 uF [T520B227M2R5AT E018]	220 uF [T520C227M2R5AT E025]
220 uF [T495E227M016AT E050]	220 uF [T498X227M010AT E500]	220 uF [T520B227M2R5AT E025]	220 uF [T520D227M004AT E012]
220 uF [T495E227M016AT E075]	220 uF [T510X227M016AT E025]	220 uF [T520B227M2R5AT E030]	220 uF [T520D227M004AT E065]
220 uF [T495E227M016AT E150]	220 uF [T510X227M016AT E040]	220 uF [T520B227M2R5AT E035]	220 uF [T520D227M006AT E006]
220 uF [T495X227M006AT E100]	220 uF [T513X227M016AH 6110]	220 uF [T520B227M2R5AT E070]	220 uF [T520D227M006AT E007]
220 uF [T495X227M010AT E045]	220 uF [T513X227M016AH 6120]	220 uF [T520C227M004AT E018]	220 uF [T520D227M006AT E009]
220 uF [T495X227M010AT E050]	220 uF [T520B227M004AT E035]	220 uF [T520C227M004AT E025]	220 uF [T520D227M006AT E015]
220 uF [T495X227M010AT E060]	220 uF [T520B227M004AT E045]	220 uF [T520C227M004AT E045]	220 uF [T520D227M006AT E040]
220 uF [T495X227M010AT E070]	220 uF [T520B227M004AT E070]	220 uF [T520C227M004AT E055]	220 uF [T520D227M006AT E050]
220 uF [T495X227M010AT E100]	220 uF [T520B227M006AT E035]	220 uF [T520C227M006AT E025]	220 uF [T520D227M010AT E018]

# Multisim 14.0 Education Components

---

220 uF [T520D227M010AT E025]	220 uF [T520V227M004AT E025]	220 uF [T520V227M2R5AT E007]	220 uF [T525D227M004AT E025]
220 uF [T520D227M010AT E040]	220 uF [T520V227M004AT E040]	220 uF [T520V227M2R5AT E009]	220 uF [T525D227M006AT E025]
220 uF [T520D227M2R5AT E007]	220 uF [T520V227M004AT E045]	220 uF [T520V227M2R5AT E012]	220 uF [T525D227M010AT E025]
220 uF [T520D227M2R5AT E040]	220 uF [T520V227M006AT E007]	220 uF [T520V227M2R5AT E015]	220 uF [T528Z227M004AT E007]
220 uF [T520U227M2R5AT E055]	220 uF [T520V227M006AT E009]	220 uF [T520V227M2R5AT E025]	220 uF [T528Z227M004AT E009]
220 uF [T520V227M004AT E006]	220 uF [T520V227M006AT E012]	220 uF [T520V227M2R5AT E045]	220 uF [T528Z227M004AT E012]
220 uF [T520V227M004AT E007]	220 uF [T520V227M006AT E015]	220 uF [T520W227M004AT E025]	220 uF [T528Z227M006AT E009]
220 uF [T520V227M004AT E009]	220 uF [T520V227M006AT E018]	220 uF [T520W227M004AT E040]	220 uF [T528Z227M006AT E012]
220 uF [T520V227M004AT E012]	220 uF [T520V227M006AT E025]	220 uF [T520Y227M010AT E040]	220 uF [T530D227M006AT E005]
220 uF [T520V227M004AT E015]	220 uF [T520V227M006AT E040]	220 uF [T522V227M006AT E025]	220 uF [T530D227M006AT E006]
220 uF [T520V227M004AT E018]	220 uF [T520V227M010AT E045]	220 uF [T522V227M006AT E040]	220 uF [T530D227M010AT E006]

# Multisim 14.0 Education Components

---

220 uF [T530D227M010AT E010]	24 pF [C1812C240KBGAC TU]	240 pF [C1210C241KBGAC TU]	27 nF [C0402C273K8RACT U]
220 uF [T530Y227M010AT E006]	24 pF [C1825C240KBGAC TU]	240 pF [C1812C241KBGAC TU]	27 nF [C0402C273K9PACT U]
220 uF [T541D227M010AH 6510]	24 pF [C1825C240KCGAC TU]	240 pF [C1825C241KBGAC TU]	27 nF [C0402C273K9RACT U]
220 uF [T543V227M004AT E015]	24 pF [C2220C240KBGAC TU]	240 pF [C2220C241KBGAC TU]	27 nF [C0603C273K1RACT U]
22GQ100	24 pF [C2225C240KBGAC TU]	240 pF [C2225C241KBGAC TU]	27 nF [C0603C273K3RACT U]
24 pF [C0402C240K4GACT U]	240 pF [C0402C241K1HACT U]	25_AMP 2-534206-0	27 nF [C0603C273K4RACT U]
24 pF [C0402C240K5GACT U]	240 pF [C0402C241K3HACT U]	27 mF [C0402C279K5GACT U]	27 nF [C0603C273K5RACT U]
24 pF [C0603C240K2GACT U]	240 pF [C0402C241K5HACT U]	27 mF [C0805C279KBGAC TU]	27 nF [C0805C273K1RACT U]
24 pF [C0805C240K5GACT U]	240 pF [C0603C241K5GACT U]	27 nF [C0402C273K3RACT U]	27 nF [C0805C273K2RACT U]
24 pF [C0805C240KBGAC TU]	240 pF [C0805C241K5GACT U]	27 nF [C0402C273K4RACT U]	27 nF [C0805C273K3HACT U]
24 pF [C1206C240KBGAC TU]	240 pF [C1206C241KBGAC TU]	27 nF [C0402C273K8PACT U]	27 nF [C0805C273K3RACT U]
24 pF [C1210C240KBGAC TU]			

# Multisim 14.0 Education Components

---

27 nF [C0805C273K4RACT U]	27 nF [C1206C273K5HACT U]	27 nF [C1210C273K5RACT U]	27 pF [C0402C270K4GACT U]
27 nF [C0805C273K5RACT U]	27 nF [C1206C273K5RACT U]	27 nF [C1210C273KARACT U]	27 pF [C0402C270K5GACT U]
27 nF [C0805C273K8RACT U]	27 nF [C1206C273KARACT U]	27 nF [C1812C273K1HACT U]	27 pF [C0402C270K8GACT U]
27 nF [C0805C273M5UAC TU]	27 nF [C1210C273K1GACT U]	27 nF [C1812C273K1RACT U]	27 pF [C0603C270K1GACT U]
27 nF [C0805F273K1RACT U]	27 nF [C1210C273K1HACT U]	27 nF [C1812C273K5HACT U]	27 pF [C0603C270K2GACT U]
27 nF [C0805F273K3RACT U]	27 nF [C1210C273K1RACT U]	27 nF [C1825C273K1GACT U]	27 pF [C0603C270K5GACT U]
27 nF [C0805F273K4RACT U]	27 nF [C1210C273K2RACT U]	27 nF [C1825C273K5GACT U]	27 pF [C0805C270K1GACT U]
27 nF [C0805F273K5RACT U]	27 nF [C1210C273K3GACT U]	27 nF [C2220C273K1GACT U]	27 pF [C0805C270K2GACT U]
27 nF [C1206C273K1HACT U]	27 nF [C1210C273K3HACT U]	27 nF [C2220C273K2GACT U]	27 pF [C0805C270K5GACT U]
27 nF [C1206C273K1RACT U]	27 nF [C1210C273K5GACT U]	27 pF [C0201C270K3GACT U]	27 pF [C0805C270KBGAC TU]
27 nF [C1206C273K3HACT U]	27 nF [C1210C273K5HACT U]	27 pF [C0402C270K3GACT U]	27 pF [C0805C270KDGAC TU]

# Multisim 14.0 Education Components

---

27 pF [C1206C270K1GACT U]	27 pF [CA064C270K8GAC TU]	270 nF [C1206C274K3RACT U]	270 nF [C1210F274K3RACT U]
27 pF [C1206C270K2GACT U]	270 nF [C0603C274K4PACT U]	270 nF [C1206C274K4RACT U]	270 nF [C1210F274K4RACT U]
27 pF [C1206C270K5GACT U]	270 nF [C0603C274K4RACT U]	270 nF [C1206C274K5RACT U]	270 nF [C1210F274K5RACT U]
27 pF [C1206C270KBGAC TU]	270 nF [C0603C274K8PACT U]	270 nF [C1206F274K3RACT U]	270 nF [C1812C274K1RACT U]
27 pF [C1210C270KBGAC TU]	270 nF [C0603C274K8RACT U]	270 nF [C1206F274K4RACT U]	270 nF [C1812C274K5RACT U]
27 pF [C1812C270KBGAC TU]	270 nF [C0603C274K9PACT U]	270 nF [C1206F274K5RACT U]	270 nF [C1812C274KARACT U]
27 pF [C1812C270KHGAC TU]	270 nF [C0603C274K9RACT U]	270 nF [C1210C274K1RACT U]	270 nF [C1812F274K1RACT U]
27 pF [C1825C270KBGAC TU]	270 nF [C0805C274K3RACT U]	270 nF [C1210C274K3RACT U]	270 nF [C1812F274K2RACT U]
27 pF [C2220C270KBGAC TU]	270 nF [C0805C274K4RACT U]	270 nF [C1210C274K5RACT U]	270 nF [C1812F274K3RACT U]
27 pF [C2225C270KBGAC TU]	270 nF [C0805C274K8RACT U]	270 nF [C1210C274M5UAC TU]	270 nF [C1812F274K5RACT U]
27 pF [CA064C270K5GAC TU]	270 nF [C1206C274K1RACT U]	270 nF [C1210F274K1RACT U]	270 nF [C1825C274K1RACT U]

# Multisim 14.0 Education Components

---

270 nF [C1825C274K5RACT U]	270 pF [C0402C271K5GACT U]	270 pF [C0805C271K1GACT U]	270 pF [C1210C271KBGAC TU]
270 nF [C2220C274K1GACT U]	270 pF [C0402C271K5HACT U]	270 pF [C0805C271K1RACT U]	270 pF [C1812C271KBGAC TU]
270 nF [C2220C274K5GACT U]	270 pF [C0402C271K5RACT U]	270 pF [C0805C271K2GACT U]	270 pF [C1825C271KBGAC TU]
270 nF [C2220C274K5RACT U]	270 pF [C0402C271K8RACT U]	270 pF [C0805C271K2RACT U]	270 pF [C2220C271KBGAC TU]
270 nF [C2225C274K1RACT U]	270 pF [C0603C271K1RACT U]	270 pF [C0805C271K4RACT U]	270 pF [C2225C271KBGAC TU]
270 nF [C2225C274K2RACT U]	270 pF [C0603C271K2RACT U]	270 pF [C0805C271K5GACT U]	270 uF [A700X277M002AT E010]
270 nF [C2225C274K5RACT U]	270 pF [C0603C271K3RACT U]	270 pF [C0805C271K5RACT U]	270 uF [A700X277M002AT E015]
270 pF [C0402C271K1HACT U]	270 pF [C0603C271K4GACT U]	270 pF [C1206C271K1GACT U]	270 uF [A700X277M004AT E010]
270 pF [C0402C271K3HACT U]	270 pF [C0603C271K4RACT U]	270 pF [C1206C271K2GACT U]	270 uF [A700X277M004AT E015]
270 pF [C0402C271K3RACT U]	270 pF [C0603C271K5GACT U]	270 pF [C1206C271K5GACT U]	27C010N120  27C010N150
270 pF [C0402C271K4RACT U]	270 pF [C0603C271K5RACT U]	270 pF [C1206C271KBGAC TU]	27C010N70  27C010N90  27C010Q120

# Multisim 14.0 Education Components

---

27C010Q150	27C128-15P	27C256-20L	27C512V120
27C010Q70	27C128-17L	27C256-20P	27C512V150
27C010Q90	27C128-17P	27C256N100	27C512V90
27C010V120	27C128-20L	27C256N120	27C64-12L
27C010V150	27C128-20P	27C256N150	27C64-12P
27C010V70	27C128-25L	27C256N200	27C64-15L
27C010V90	27C128-25P	27C256N90	27C64-15P
27C020N100	27C128N120	27C256Q100	27C64-17L
27C020N120	27C128N150	27C256Q120	27C64-17P
27C020N150	27C128N200	27C256Q150	27C64-20L
27C020Q100	27C128N90	27C256Q200	27C64-20P
27C020Q120	27C128Q120	27C256Q90	27C64-25L
27C020Q150	27C128Q150	27C256V100	27C64-25P
27C020V100	27C128Q200	27C256V120	27C64E200-883
27C020V120	27C128Q90	27C256V150	27C64E250-883
27C020V150	27C128V120	27C256V200	27C64E350-883
27C040N120	27C128V150	27C256V90	27C64N150
27C040N150	27C128V200	27C32BQ150	27C64N200
27C040Q120	27C128V90	27C32BQ200	27C64Q150
27C040Q150	27C16BQ150	27C512N120	27C64Q200
27C040V120	27C16BQ200	27C512N150	27C64Q200-883
27C040V150	27C256-12L	27C512N90	27C64Q250-883
27C128-12L	27C256-12P	27C512Q120	27C64Q350-883
27C128-12P	27C256-15L	27C512Q150	282834-2
27C128-15L	27C256-15P	27C512Q90	282834-4

# Multisim 14.0 Education Components

---

282834-5	2N3055G	2N3711	2N3906G
282834-8	2N3370	2N3771G	2N3921
28V_7.5W	2N3390	2N3772G	2N3922
292303-1	2N3391	2N3773G	2N3954
292304-1	2N3391A	2N3821	2N3954A
2A3	2N3392	2N3822	2N3955
2K8RAM	2N3393	2N3823	2N3955A
2N1599	2N3394	2N3824	2N3956
2N2222A	2N3414	2N3858A	2N3957
2N2573	2N3415	2N3859	2N3958
2N2574	2N3416	2N3859A	2N3966
2N2575	2N3417	2N3860	2N3967
2N2576	2N3442G	2N3870	2N3970
2N2577	2N3458	2N3871	2N3971
2N2578	2N3459	2N3872	2N3972
2N2579	2N3668	2N3873	2N4058
2N2608	2N3669	2N3896	2N4061
2N2609	2N3670	2N3897	2N4062
2N2712	2N3684	2N3898	2N4084
2N2714	2N3685	2N3899	2N4091
2N2923	2N3686	2N3903	2N4092
2N2924	2N3687	2N3904	2N4093
2N2925	2N3702	2N3904G	2N4117A
2N3055A	2N3703	2N3905	2N4118A
2N3055AG	2N3707	2N3906	2N4119A



# Multisim 14.0 Education Components

---

2N4123	2N4204	2N4416	2N5018
2N4124	2N4220	2N4416A	2N5019
2N4125	2N4220A	2N4424	2N5020
2N4126	2N4221	2N4441	2N5021
2N4167	2N4221A	2N4442	2N5038G
2N4168	2N4222	2N4443	2N5045
2N4169	2N4222A	2N4444	2N5046
2N4170	2N4223	2N4856	2N5047
2N4171	2N4286	2N4856A	2N5060
2N4172	2N4289	2N4857	2N5061
2N4173	2N4291	2N4857A	2N5062
2N4174	2N4338	2N4858	2N5063
2N4183	2N4339	2N4858A	2N5064
2N4184	2N4340	2N4859	2N5078
2N4185	2N4341	2N4859A	2N5086
2N4186	2N4381	2N4860	2N5087
2N4187	2N4391	2N4860A	2N5088
2N4188	2N4392	2N4861	2N5089
2N4189	2N4393	2N4861A	2N5103
2N4190	2N4400	2N4918G	2N5105
2N4199	2N4401	2N4919G	2N5114
2N4200	2N4402	2N4920G	2N5115
2N4201	2N4403	2N4921G	2N5116
2N4202	2N4409	2N4922G	2N5168
2N4203	2N4410	2N4923G	2N5169

# Multisim 14.0 Education Components

---

2N5170	2N5398	2N5545	2N5885G
2N5171	2N5400	2N5550	2N5886G
2N5172	2N5401	2N5550G	2N6027
2N5191G	2N5432	2N5550RLRPG	2N6027G
2N5192G	2N5433	2N5551	2N6027RL1G
2N5194G	2N5434	2N5556	2N6027RLRAG
2N5195G	2N5444	2N5557	2N6028
2N5196	2N5445	2N5558	2N6028G
2N5197	2N5446	2N5564	2N6028RLRAG
2N5199	2N5447	2N5565	2N6028RLRMG
2N5209	2N5452	2N5566	2N6028RLRPG
2N5210	2N5454	2N5567	2N6034G
2N5223	2N5484	2N5568	2N6035G
2N5224	2N5485	2N5571	2N6036G
2N5226	2N5486	2N5572	2N6038G
2N5227	2N5515	2N5655G	2N6039G
2N5232	2N5516	2N5657G	2N6040G
2N5232A	2N5517	2N5684G	2N6042G
2N5302G	2N5518	2N5686G	2N6043G
2N5354	2N5519	2N5769	2N6045G
2N5355	2N5520	2N5771	2N6052G
2N5358	2N5521	2N5817	2N6071
2N5365	2N5522	2N5830	2N6073BG
2N5366	2N5523	2N5883G	2N6107G
2N5397	2N5524	2N5884G	2N6109G

# Multisim 14.0 Education Components

---

2N6111G	2N6292G	2N6487G	2N7002LT3G
2N6145	2N6338G	2N6488G	2N7002P
2N6146	2N6341G	2N6490G	2N7002PS
2N6147	2N6342	2N6491G	2N7002PT
2N6157	2N6343	2N6667G	2N7002PV
2N6158	2N6344	2N6715	2N7002PW
2N6159	2N6345	2N6727	2N7269
2N6160	2N6346	2N7000	2P1S
2N6161	2N6347	2N7000G	2P2S
2N6162	2N6348	2N7000RLRAG	2P3S
2N6163	2N6349	2N7002	2P4S
2N6164	2N6387G	2N7002BK	2P5S
2N6165	2N6388G	2N7002BKM	2PA1576Q
2N6167	2N6394	2N7002BKMB	2PA1576R
2N6168	2N6395	2N7002BKS	2PA1576S
2N6169	2N6396	2N7002BKT	2PA1774Q
2N6170	2N6397	2N7002BKV	2PA1774QM
2N6171	2N6398	2N7002BKW	2PA1774QMB
2N6172	2N6399	2N7002CK	2PA1774R
2N6173	2N6400	2N7002DW	2PA1774RM
2N6174	2N6401	2N7002E	2PA1774RMB
2N6284G	2N6402	2N7002ET1G	2PA1774S
2N6286G	2N6403	2N7002F	2PA1774SM
2N6287G	2N6404	2N7002K	2PA1774SMB
2N6288G	2N6405	2N7002LT1G	2PB1219AQ

# Multisim 14.0 Education Components

---

2PB1219AR	2PD601ART	2SA733	2SC5706-TL-H
2PB1219AS	2PD601ARW	2SA952	2SC5964-TD-E
2PB1424	2PD601ASL	2SA953	2SC5964-TD-H
2PB709ARL	2PD601ASW	2SA954	2SC945
2PB709ART	2PD601BRL	2SB1205S-TL-E	2SD1623S-TD-E
2PB709ARW	2PD601BSL	2SB1205T-TL-E	2SD1623T-TD-E
2PB709ASL	2PD602AQL	2SC1815	2SD1628F-TD-E
2PB709ASW	2PD602ARL	2SC2001	2SD1628F-TD-H
2PB709BRL	2PD602ASL	2SC2120	2SD1628G-TD-E
2PB709BSL	2SA1015	2SC2240	2SD1628G-TD-H
2PB710ARL	2SA1020	2SC2655	2SD1805F-E
2PB710ASL	2SA1213	2SC2786	2SD1805F-TL-E
2PC4081Q	2SA1416S-TD-E	2SC2873	2SD1805G-E
2PC4081R	2SA1416T-TD-E	2SC3649S-TD-E	2SD1805G-TL-E
2PC4081S	2SA1460	2SC3649S-TD-H	2SD1815S-E
2PC4617Q	2SA1507S	2SC3649T-TD-E	2SD1815S-TL-E
2PC4617QM	2SA1507T	2SC3649T-TD-H	2SD1815T-E
2PC4617QMB	2SA1774G	2SC3733	2SD1815T-TL-E
2PC4617R	2SA1774T1G	2SC4617G	2SJ517
2PC4617RM	2SA2126-E	2SC4617T1G	2SJ652
2PC4617RMB	2SA2126-H	2SC5566-TD-E	2SJ652-RA11
2PD1820AR	2SA2126-TL-E	2SC5658M3T5G	2SJ661-E
2PD1820AS	2SA2126-TL-H	2SC5706-E	2SJ665-DL-E
2PD2150	2SA2205-E	2SC5706-H	2SK117
2PD601ARL	2SA2205-TL-E	2SC5706-TL-E	2SK170

# Multisim 14.0 Education Components

---

2SK192A	2SK3703	3 nF [C0805C302K3GACT U]	3.3 nF [C0603C332K1HACT U]
2SK208	2SK3704		
2SK209	2SK3746	3 nF [C0805C302K3HACT U]	3.3 nF [C0603C332K1RACT U]
2SK2553L	2SK3746-1E		
2SK2553S	2SK3747	3 nF [C0805C302K5HACT U]	3.3 nF [C0603C332K3GACT U]
2SK2978	2SK3747-1E		
2SK2980	2SK3748	3 nF [C1825C302KBGAC TU]	3.3 nF [C0603C332K3HACT U]
2SK3069	2SK3748-1E		
2SK3070L	2SK3820-DL-E	3 nF [C2220C302KBGAC TU]	3.3 nF [C0603C332K3RACT U]
2SK3070S	2SK3820-E		
2SK30ATM	2SWITCHCM		
2SK3133	2V7002LT1G	3 nF [C2225C302KBGAC TU]	3.3 nF [C0603C332K4RACT U]
2SK3134	2V7002LT3G		
2SK3135	3 nF [C0603C302K1HACT U]	3.3 nF [C0402C332K3RACT U]	3.3 nF [C0603C332K5HACT U]
2SK3136			
2SK3140	3 nF [C0603C302K3HACT U]	3.3 nF [C0402C332K4RACT U]	3.3 nF [C0603C332K5RACT U]
2SK3141			
2SK3142	3 nF [C0603C302K5HACT U]	3.3 nF [C0402C332K5RACT U]	3.3 nF [C0805C332K1GACT U]
2SK3203			
2SK3233	3 nF [C0805C302K1GACT U]	3.3 nF [C0402C332K8RACT U]	3.3 nF [C0805C332K1HACT U]
2SK330			
2SK364	3 nF [C0805C302K1HACT U]	3.3 nF [C0402C332K9RACT U]	3.3 nF [C0805C332K1RACT U]
2SK366			
2SK367			
2SK368			

# Multisim 14.0 Education Components

---

3.3 nF [C0805C332K2RACT U]	3.3 nF [C1206C332K1RACT U]	3.3 nF [C2225C332KBGAC TU]	3.3 uF [C1206C335K9PACT U]
3.3 nF [C0805C332K3GACT U]	3.3 nF [C1206C332K2RACT U]	3.3 nF [CA064C332K1RACT U]	3.3 uF [C1206C335K9RACT U]
3.3 nF [C0805C332K3HACT U]	3.3 nF [C1206C332K3RACT U]	3.3 nF [CA064C332K5RACT U]	3.3 uF [C1206C335M4VAC TU]
3.3 nF [C0805C332K4GACT U]	3.3 nF [C1206C332K5GACT U]	3.3 uF [C0805C335K4PACT U]	3.3 uF [C1206C335M9VAC TU]
3.3 nF [C0805C332K4RACT U]	3.3 nF [C1206C332K5RACT U]	3.3 uF [C0805C335K8PACT U]	3.3 uF [C1210C335K3PACT U]
3.3 nF [C0805C332K5GACT U]	3.3 nF [C1210C332K1RACT U]	3.3 uF [C0805C335K9PACT U]	3.3 uF [C1210C335K4PACT U]
3.3 nF [C0805C332K5HACT U]	3.3 nF [C1210C332K2GACT U]	3.3 uF [C1206C335K3PACT U]	3.3 uF [C1210C335K4RACT U]
3.3 nF [C0805C332K5RACT U]	3.3 nF [C1210C332K5GACT U]	3.3 uF [C1206C335K4PACT U]	3.3 uF [C1210C335K8PACT U]
3.3 nF [C0805C332K8GACT U]	3.3 nF [C1210C332K5RACT U]	3.3 uF [C1206C335K4RACT U]	3.3 uF [T409B335M006AH 4250]
3.3 nF [C0805C332KARACT U]	3.3 nF [C1825C332KBGAC TU]	3.3 uF [C1206C335K8PACT U]	3.3 uF [T489A335M020AT E3K7]
3.3 nF [C1206C332K1GACT U]	3.3 nF [C2220C332KBGAC TU]	3.3 uF [C1206C335K8RACT U]	3.3 uF [T491A335M004AT]  3.3 uF [T491A335M006AT]

# Multisim 14.0 Education Components

---

3.3 uF [T491A335M010AT]	3.3 uF [T494A335M004AT]	3.3 uF [T495B335M035AT E900]	3.6 nF [C0805C362K1HACT U]
3.3 uF [T491A335M016AT]	3.3 uF [T494A335M006AT]	3.3 uF [T495C335M035AT E525]	3.6 nF [C0805C362K3HACT U]
3.3 uF [T491A335M020AT]	3.3 uF [T494A335M010AT]	3.3 uF [T495C335M035AT E550]	3.6 nF [C0805C362K5HACT U]
3.3 uF [T491B335M016AT]	3.3 uF [T494A335M016AT]	3.3 uF [T495C335M035AT E600]	3.6 nF [C1825C362KBGAC TU]
3.3 uF [T491B335M020AT]	3.3 uF [T494A335M020AT]	3.3 uF [T498A335M010AT E3K6]	3.6 nF [C2220C362KBGAC TU]
3.3 uF [T491B335M025AT]	3.3 uF [T494B335M016AT]	3.3 uF [T498A335M016AT E3K4]	3.6 nF [C2225C362KBGAC TU]
3.3 uF [T491B335M035AT]	3.3 uF [T494B335M020AT]	3.3 uF [T498C335M035AT E1K7]	3.9 nF [C0402C392K3RACT U]
3.3 uF [T491C335M025AT]	3.3 uF [T494B335M025AT]	3.6 nF [C0603C362K1HACT U]	3.9 nF [C0402C392K4RACT U]
3.3 uF [T491C335M035AT]	3.3 uF [T494C335M025AT]	3.6 nF [C0603C362K3HACT U]	3.9 nF [C0402C392K5RACT U]
3.3 uF [T491D335M035AT ]	3.3 uF [T494C335M035AT]	3.6 nF [C0603C362K5HACT U]	3.9 nF [C0603C392K1HACT U]
3.3 uF [T491D335M050AT ]	3.3 uF [T494D335M050AT ]	3.6 nF [C0805C362K1GACT U]	3.9 nF [C0603C392K1RACT U]
3.3 uF [T491S335M010AT]	3.3 uF [T494S335M010AT]		
3.3 uF [T491T335M020AT]	3.3 uF [T494T335M020AT]		
3.3 uF [T493A335M004AH 6110]	3.3 uF [T495A335M016AT E3K0]		

# Multisim 14.0 Education Components

---

3.9 nF [C0603C392K3GACT U]	3.9 nF [C0805C392K3HACT U]	3.9 nF [C1206C392K5GACT U]	3.9 uF [C1206C395K9RACT U]
3.9 nF [C0603C392K3HACT U]	3.9 nF [C0805C392K3RACT U]	3.9 nF [C1206C392K5RACT U]	3.9 uF [C1210C395K3NAC TU]
3.9 nF [C0603C392K3RACT U]	3.9 nF [C0805C392K4GACT U]	3.9 nF [C1210C392K5RACT U]	3_AMP  30 mF [C0402C309K5GACT U]
3.9 nF [C0603C392K4RACT U]	3.9 nF [C0805C392K4RACT U]	3.9 nF [C1812C392K2GACT U]	30 mF [C0805C309KBGAC TU]
3.9 nF [C0603C392K5HACT U]	3.9 nF [C0805C392K5GACT U]	3.9 nF [C1825C392KBGAC TU]	30 pF [C0402C300K5GACT U]
3.9 nF [C0603C392K5RACT U]	3.9 nF [C0805C392K5HACT U]	3.9 nF [C2220C392KBGAC TU]	30 pF [C0603C300K2GACT U]
3.9 nF [C0805C392K1GACT U]	3.9 nF [C0805C392K5RACT U]	3.9 nF [C2225C392KBGAC TU]	30 pF [C0603C300K5GACT U]
3.9 nF [C0805C392K1HACT U]	3.9 nF [C0805C392KARACT U]	3.9 nF [C2225C392KCGAC TU]	30 pF [C0805C300K2GACT U]
3.9 nF [C0805C392K1RACT U]	3.9 nF [C1206C392K1GACT U]	3.9 nF [CDR02BX392BKSM ]	30 pF [C0805C300K5GACT U]
3.9 nF [C0805C392K2RACT U]	3.9 nF [C1206C392K1RACT U]	3.9 uF [C1206C395K4RACT U]	30 pF [C0805C300KBGAC TU]
3.9 nF [C0805C392K3GACT U]	3.9 nF [C1206C392K2RACT U]	3.9 uF [C1206C395K8RACT U]	30 pF [C1206C300K1GACT U]



# Multisim 14.0 Education Components

---

30 pF [C1206C300K5GACT U]	300 pF [C0805C301K2GACT U]	30LJQ150  30SCLJQ030	33 nF [C0402C333K9RACT U]
30 pF [C1206C300KBGAC TU]	300 pF [C0805C301K5GACT U]	30SCLJQ060  30SLJQ030	33 nF [C0603C333K1RACT U]
30 pF [C1210C300KBGAC TU]	300 pF [C1206C301K5GACT U]	30V_10W  3280A	33 nF [C0603C333K3RACT U]
30 pF [C1812C300KBGAC TU]	300 pF [C1206C301KBGAC TU]	3288RT  32CTQ030	33 nF [C0603C333K4RACT U]
30 pF [C1825C300KBGAC TU]	300 pF [C1210C301KBGAC TU]	33 mF [C0805C339KBGAC TU]	33 nF [C0603C333K5RACT U]
30 pF [C2220C300KBGAC TU]	300 pF [C1812C301KBGAC TU]	33 mF [C1206C339K5GACT U]	33 nF [C0603C333K8RACT U]
30 pF [C2225C300KBGAC TU]	300 pF [C1825C301KBGAC TU]	33 nF [C0402C333K3RACT U]	33 nF [C0603C333M3VAC TU]
30_AMP	300 pF [C2220C301KBGAC TU]	33 nF [C0402C333K4RACT U]	33 nF [C0805C333K1RACT U]
300 pF [C0402C301K1HACT U]	300 pF [C2225C301KBGAC TU]	33 nF [C0402C333K8PACT U]	33 nF [C0805C333K2RACT U]
300 pF [C0402C301K3HACT U]	30CLJQ045	33 nF [C0402C333K8RACT U]	33 nF [C0805C333K3GACT U]
300 pF [C0402C301K5HACT U]	30CLJQ100	33 nF [C0402C333K9PACT U]	33 nF [C0805C333K3HACT U]
300 pF [C0805C301K1GACT U]	30CLJQ150		
	30LJQ045		
	30LJQ100		

# Multisim 14.0 Education Components

---

33 nF [C0805C333K3RACT U]	33 nF [C1206C333K2RACT U]	33 nF [C1210C333K2RACT U]	33 nF [C1812C333K5GACT U]
33 nF [C0805C333K4RACT U]	33 nF [C1206C333K3GACT U]	33 nF [C1210C333K3GACT U]	33 nF [C1812C333K5HACT U]
33 nF [C0805C333K5RACT U]	33 nF [C1206C333K3HACT U]	33 nF [C1210C333K3HACT U]	33 nF [C1812C333K5RACT U]
33 nF [C0805C333K8RACT U]	33 nF [C1206C333K5HACT U]	33 nF [C1210C333K5GACT U]	33 nF [C1825C333K1RACT U]
33 nF [C0805C333M5UAC TU]	33 nF [C1206C333K5RACT U]	33 nF [C1210C333K5HACT U]	33 nF [C1825C333K5RACT U]
33 nF [C0805F333K1RACT U]	33 nF [C1206C333KARACT U]	33 nF [C1210C333K5RACT U]	33 nF [C2220C333K1GACT U]
33 nF [C0805F333K3RACT U]	33 nF [C1206C333M1UAC TU]	33 nF [C1210C333KARACT U]	33 nF [C2220C333K2GACT U]
33 nF [C0805F333K4RACT U]	33 nF [C1206C333M5UAC TU]	33 nF [C1812C333K1GACT U]	33 nF [C2220C333K5GACT U]
33 nF [C0805F333K5RACT U]	33 nF [C1210C333K1GACT U]	33 nF [C1812C333K1HACT U]	33 nF [C2225C333K5GACT U]
33 nF [C1206C333K1HACT U]	33 nF [C1210C333K1HACT U]	33 nF [C1812C333K1RACT U]	33 nF [CA064C333K4RACT U]
33 nF [C1206C333K1RACT U]	33 nF [C1210C333K1RACT U]	33 nF [C1812C333K2RACT U]	33 pF [C0201C330K3GACT U]

# Multisim 14.0 Education Components

---

33 pF [C0402C330K3GACT U]	33 pF [C0805C330KBGAC TU]	33 pF [C1825C330KBGAC TU]	33 uF [A700V336M010AT E018]
33 pF [C0402C330K4GACT U]	33 pF [C0805C330KDGAC TU]	33 pF [C2220C330KBGAC TU]	33 uF [A700V336M010AT E025]
33 pF [C0402C330K5GACT U]	33 pF [C1206C330K1GACT U]	33 pF [C2225C330KBGAC TU]	33 uF [A700V336M010AT E028]
33 pF [C0402C330K8GACT U]	33 pF [C1206C330K2GACT U]	33 pF [CA064C330K5GAC TU]	33 uF [T409F336M004AH 4250]
33 pF [C0603C330K1GACT U]	33 pF [C1206C330K5GACT U]	33 pF [CA064C330K8GAC TU]	33 uF [T409G336M010AH 4250]
33 pF [C0603C330K2GACT U]	33 pF [C1206C330KBGAC TU]	33 uF [A700V336M006AT E018]	33 uF [T419E336M006AH 4250]
33 pF [C0603C330K3GACT U]	33 pF [C1206C330KCGAC TU]	33 uF [A700V336M006AT E025]	33 uF [T419X336M025AH 4250]
33 pF [C0603C330K5GACT U]	33 pF [C1206C330KDGAC TU]	33 uF [A700V336M006AT E028]	33 uF [T489D336M020AT E250]
33 pF [C0805C330K1GACT U]	33 pF [C1206C330KGGAC TU]	33 uF [A700V336M008AT E018]	33 uF [T491A336M003AT]
33 pF [C0805C330K2GACT U]	33 pF [C1210C330KBGAC TU]	33 uF [A700V336M008AT E025]	33 uF [T491A336M004AT]
33 pF [C0805C330K5GACT U]	33 pF [C1812C330KBGAC TU]	33 uF [A700V336M008AT E028]	33 uF [T491A336M006AT]
			33 uF [T491A336M010AT]

# Multisim 14.0 Education Components

---

33 uF [T491B336M004AT]	33 uF [T491D336M035AT ]	33 uF [T494A336M004AT]	33 uF [T494D336M020AT ]
33 uF [T491B336M006AT]	33 uF [T491T336M004AT]	33 uF [T494A336M006AT]	33 uF [T494D336M025AT ]
33 uF [T491B336M010AT]	33 uF [T491T336M006AT]	33 uF [T494A336M010AT]	33 uF [T494D336M035AT ]
33 uF [T491B336M016AT]	33 uF [T491T336M010AT]	33 uF [T494B336M004AT]	33 uF [T494T336M004AT]
33 uF [T491C336M004AT]	33 uF [T491U336M004AT ]	33 uF [T494B336M006AT]	33 uF [T494T336M006AT]
33 uF [T491C336M006AT]	33 uF [T491U336M006AT ]	33 uF [T494C336M004AT]	33 uF [T494T336M010AT]
33 uF [T491C336M010AT]	33 uF [T491U336M010AT ]	33 uF [T494C336M006AT]	33 uF [T494U336M004AT ]
33 uF [T491C336M016AT]	33 uF [T491U336M016AT ]	33 uF [T494C336M010AT]	33 uF [T494U336M006AT ]
33 uF [T491C336M020AT]	33 uF [T491V336M010AT]	33 uF [T494C336M020AT]	33 uF [T494U336M010AT ]
33 uF [T491C336M025AT]	33 uF [T491V336M020AT]	33 uF [T494C336M025AT]	33 uF [T494U336M016AT ]
33 uF [T491D336M010AT ]	33 uF [T491X336M025AT]	33 uF [T494D336M010AT ]	33 uF [T494V336M010AT]
33 uF [T491D336M016AT ]	33 uF [T491X336M035AT]	33 uF [T494D336M016AT ]	33 uF [T494V336M020AT]
33 uF [T491D336M020AT ]	33 uF [T494A336M003AT]		33 uF [T494X336M025AT]
33 uF [T491D336M025AT ]			

# Multisim 14.0 Education Components

---

33 uF [T494X336M035AT]	33 uF [T495E336M035AT E200]	33 uF [T498D336M016AT E600]	33 uF [T520B336M006AT E040]
33 uF [T495B336M010AT E450]	33 uF [T495V336M010AT E100]	33 uF [T498D336M025AT E600]	33 uF [T520B336M006AT E070]
33 uF [T495C336M016AT E200]	33 uF [T495V336M010AT E150]	33 uF [T498X336M035AT E500]	33 uF [T520B336M008AT E025]
33 uF [T495C336M016AT E275]	33 uF [T495X336M025AT E100]	33 uF [T510X336M035AT E050]	33 uF [T520B336M008AT E035]
33 uF [T495D336M016AT E225]	33 uF [T495X336M025AT E175]	33 uF [T510X336M035AT E065]	33 uF [T520B336M008AT E040]
33 uF [T495D336M020AT E100]	33 uF [T495X336M025AT E200]	33 uF [T520A336M004AT E070]	33 uF [T520B336M008AT E070]
33 uF [T495D336M020AT E200]	33 uF [T495X336M035AT E100]	33 uF [T520A336M004AT E080]	33 uF [T520B336M010AT E035]
33 uF [T495D336M025AT E090]	33 uF [T495X336M035AT E175]	33 uF [T520A336M006AT E070]	33 uF [T520B336M010AT E040]
33 uF [T495D336M025AT E100]	33 uF [T495X336M035AT E250]	33 uF [T520A336M006AT E080]	33 uF [T520B336M010AT E070]
33 uF [T495D336M025AT E225]	33 uF [T497H336M015AT 6110]	33 uF [T520B336M006AT E025]	33 uF [T520C336M006AT E100]
33 uF [T495D336M025AT E300]	33 uF [T498B336M006AT E1K7]	33 uF [T520B336M006AT E035]	33 uF [T520T336M006AT E070]

# Multisim 14.0 Education Components

---

33 uF [T520T336M008AT E070]	33 uF [T521D336M035AT E065]	330 nF [C0603C334K4RACT U]	330 nF [C1206C334K1RACT U]
33 uF [T520T336M008AT E080]	33 uF [T521V336M025AT E060]	330 nF [C0603C334K8PACT U]	330 nF [C1206C334K3RACT U]
33 uF [T520T336M010AT E070]	33 uF [T525B336M006AT E080]	330 nF [C0603C334K8RACT U]	330 nF [C1206C334K4RACT U]
33 uF [T520T336M010AT E080]	33 uF [T525B336M010AT E080]	330 nF [C0603C334K9RACT U]	330 nF [C1206C334K5RACT U]
33 uF [T520U336M008AT E070]	33 uF [T525T336M008AT E080]	330 nF [C0805C334K3NAC TU]	330 nF [C1206C334M3VAC TU]
33 uF [T520U336M010AT E070]	33 uF [T525T336M010AT E080]	330 nF [C0805C334K3RACT U]	330 nF [C1206F334K3RACT U]
33 uF [T520V336M016AT E045]	33 uF [T528I336M010ATE 150]	330 nF [C0805C334K4RACT U]	330 nF [C1206F334K4RACT U]
33 uF [T520V336M016AT E060]	33 uF [T541X336M050AH 6510]	330 nF [C0805C334K8RACT U]	330 nF [C1210C334K1RACT U]
33 uF [T520V336M016AT E070]	33 uF [T543A336M004AT E070]	330 nF [C0805C334M3VAC TU]	330 nF [C1210C334K3RACT U]
33 uF [T520W336M016AT E045]	33 uF [T543B336M010AT E040]	330 nF [C0805C334M4VAC TU]	330 nF [C1210C334K5RACT U]
33 uF [T521D336M025AT E060]	330 nF [C0603C334K4PACT U]	330 nF [C0805C334M8VAC TU]	330 nF [C1210C334M5UAC TU]

# Multisim 14.0 Education Components

---

330 nF [C1210C334M5VAC TU]	330 nF [C1812F334K3RACT U]	330 nF [C2225C334K1RACT U]	330 pF [C0402C331K3HACT U]
330 nF [C1210F334K1RACT U]	330 nF [C1812F334K5RACT U]	330 nF [C2225C334K2RACT U]	330 pF [C0402C331K3RACT U]
330 nF [C1210F334K3RACT U]	330 nF [C1825C334K1RACT U]	330 nF [C2225C334K5RACT U]	330 pF [C0402C331K4GACT U]
330 nF [C1210F334K4RACT U]	330 nF [C1825C334K2RACT U]	330 nF [C2225C334M5UAC TU]	330 pF [C0402C331K4RACT U]
330 nF [C1210F334K5RACT U]	330 nF [C1825C334K5RACT U]	330 nF [T409A334M025AH 4250]	330 pF [C0402C331K5GACT U]
330 nF [C1812C334K1RACT U]	330 nF [C1825C334M5UAC TU]	330 nF [T491A334M025AT]	330 pF [C0402C331K5HACT U]
330 nF [C1812C334K5RACT U]	330 nF [C2220C334K1GACT U]	330 nF [T491A334M035AT]	330 pF [C0402C331K5RACT U]
330 nF [C1812C334KARACT U]	330 nF [C2220C334K1RACT U]	330 nF [T494A334M025AT]	330 pF [C0402C331K8RACT U]
330 nF [C1812C334M5UAC TU]	330 nF [C2220C334K2RACT U]	330 nF [T494A334M035AT]	330 pF [C0603C331K1RACT U]
330 nF [C1812F334K1RACT U]	330 nF [C2220C334K5GACT U]	330 nF [T496B334M050AT 6110]	330 pF [C0603C331K2RACT U]
330 nF [C1812F334K2RACT U]	330 nF [C2220C334K5RACT U]	330 pF [C0402C331K1HACT U]	330 pF [C0603C331K3GACT U]

# Multisim 14.0 Education Components

---

330 pF [C0603C331K3RACT U]	330 pF [C0805C331K4RACT U]	330 pF [C1210C331KBGAC TU]	330 uF [A700X337M004AT E015]
330 pF [C0603C331K4RACT U]	330 pF [C0805C331K5GACT U]	330 pF [C1812C331KBGAC TU]	330 uF [A700X337M2R5AT E010]
330 pF [C0603C331K5GACT U]	330 pF [C0805C331K5RACT U]	330 pF [C1825C331KBGAC TU]	330 uF [A700X337M2R5AT E015]
330 pF [C0603C331K5RACT U]	330 pF [C0805C331K8RACT U]	330 pF [C2220C331KBGAC TU]	330 uF [T489X337M010AT E100]
330 pF [C0603C331K8RACT U]	330 pF [C1206C331K1GACT U]	330 pF [C2225C331KBGAC TU]	330 uF [T491C337M004AT]
330 pF [C0805C331K1GACT U]	330 pF [C1206C331K2GACT U]	330 pF [CA064C331K5GAC TU]	330 uF [T491D337M004AT ]
330 pF [C0805C331K1RACT U]	330 pF [C1206C331K5GACT U]	330 pF [CA064C331K5RACT U]	330 uF [T491D337M006AT ]
330 pF [C0805C331K2GACT U]	330 pF [C1206C331KBGAC TU]	330 uF [A700D337M002AT E007]	330 uF [T491D337M010AT ]
330 pF [C0805C331K2RACT U]	330 pF [C1206C331KCGAC TU]	330 uF [A700X337M002AT E010]	330 uF [T491E337M006AT]
330 pF [C0805C331K3GACT U]	330 pF [C1210C331K1GACT U]	330 uF [A700X337M002AT E015]	330 uF [T491V337M004AT]
330 pF [C0805C331K3RACT U]	330 pF [C1210C331K5GACT U]	330 uF [A700X337M004AT E010]	330 uF [T491X337M006AT]
			330 uF [T491X337M010AT]



# Multisim 14.0 Education Components

---

330 uF [T494C337M004AT]	330 uF [T495D337M006AT E100]	330 uF [T495X337M010AT E100]	330 uF [T520D337M004AT E009]
330 uF [T494D337M004AT ]	330 uF [T495D337M010AT E100]	330 uF [T510X337M010AT E035]	330 uF [T520D337M004AT E012]
330 uF [T494D337M006AT ]	330 uF [T495D337M010AT E125]	330 uF [T513X337M010AH 6110]	330 uF [T520D337M004AT E015]
330 uF [T494D337M010AT ]	330 uF [T495D337M010AT E150]	330 uF [T520B337M2R5AT E045]	330 uF [T520D337M004AT E040]
330 uF [T494E337M006AT]	330 uF [T495E337M010AT E060]	330 uF [T520B337M2R5AT E070]	330 uF [T520D337M004AT E045]
330 uF [T494V337M004AT]	330 uF [T495X337M006AT E045]	330 uF [T520C337M004AT E025]	330 uF [T520D337M006AT E009]
330 uF [T494X337M006AT]	330 uF [T495X337M006AT E065]	330 uF [T520C337M2R5AT E015]	330 uF [T520D337M006AT E010]
330 uF [T494X337M010AT]	330 uF [T495X337M006AT E100]	330 uF [T520C337M2R5AT E025]	330 uF [T520D337M006AT E015]
330 uF [T495D337M004AT E030]	330 uF [T495X337M010AT E035]	330 uF [T520C337M2R5AT E045]	330 uF [T520D337M006AT E025]
330 uF [T495D337M006AT E050]	330 uF [T495X337M010AT E050]	330 uF [T520D337M004AT E006]	330 uF [T520D337M006AT E040]
330 uF [T495D337M006AT E070]	330 uF [T495X337M010AT E060]	330 uF [T520D337M004AT E007]	330 uF [T520D337M006AT E045]

# Multisim 14.0 Education Components

---

330 uF [T520D337M2R5AT E006]	330 uF [T520V337M004AT E012]	330 uF [T520V337M2R5AT E015]	330 uF [T520Y337M006AT E040]
330 uF [T520D337M2R5AT E007]	330 uF [T520V337M004AT E018]	330 uF [T520V337M2R5AT E018]	330 uF [T520Y337M010AT E015]
330 uF [T520L337M2R5AT E009]	330 uF [T520V337M004AT E025]	330 uF [T520V337M2R5AT E025]	330 uF [T520Y337M010AT E035]
330 uF [T520L337M2R5AT E012]	330 uF [T520V337M004AT E040]	330 uF [T520V337M2R5AT E040]	330 uF [T522V337M006AT E040]
330 uF [T520L337M2R5AT E025]	330 uF [T520V337M006AT E015]	330 uF [T520W337M2R5A TE025]	330 uF [T525D337M003AT E025]
330 uF [T520V337M003AT E009]	330 uF [T520V337M006AT E025]	330 uF [T520W337M2R5A TE040]	330 uF [T525D337M004AT E025]
330 uF [T520V337M003AT E012]	330 uF [T520V337M006AT E040]	330 uF [T520X337M010AT E010]	330 uF [T525D337M006AT E025]
330 uF [T520V337M003AT E015]	330 uF [T520V337M2R5AT E006]	330 uF [T520X337M010AT E025]	330 uF [T525D337M006AT E040]
330 uF [T520V337M003AT E025]	330 uF [T520V337M2R5AT E007]	330 uF [T520X337M010AT E040]	330 uF [T525D337M2R5AT E025]
330 uF [T520V337M004AT E007]	330 uF [T520V337M2R5AT E009]	330 uF [T520Y337M006AT E015]	330 uF [T528Z337M004AT E009]
330 uF [T520V337M004AT E009]	330 uF [T520V337M2R5AT E012]	330 uF [T520Y337M006AT E025]	330 uF [T528Z337M004AT E012]

# Multisim 14.0 Education Components

---

330 uF [T528Z337M2R5AT E005]	330 uF [T530X337M010AT E010]	35GQ150  35SCGQ030	360 pF [C0402C361K1HACT U]
330 uF [T528Z337M2R5AT E007]	330 uF [T530Y337M006AT E006]	35SCGQ060  35SGQ060	360 pF [C0402C361K3HACT U]
330 uF [T528Z337M2R5AT E008]	330 uF [T541X337M010AH 6520]	36 mF [C0805C369KBGAC TU]	360 pF [C0402C361K5HACT U]
330 uF [T528Z337M2R5AT E009]	330 uF [T541Y337M006AH 6510]	36 pF [C0805C360KBGAC TU]	360 pF [C0603C361K5GACT U]
330 uF [T528Z337M2R5AT E012]	330 uF [T543C337M2R5AT E045]	36 pF [C1206C360KBGAC TU]	360 pF [C1206C361KBGAC TU]
330 uF [T530D337M004AT E006]	330 uF [T543L337M2R5AT E025]	36 pF [C1210C360KBGAC TU]	360 pF [C1210C361KBGAC TU]
330 uF [T530D337M006AT E006]	330 uF [T543Y337M006AT E015]	36 pF [C1812C360KBGAC TU]	360 pF [C1812C361KBGAC TU]
330 uF [T530D337M006AT E010]	3-534206-0  3554AM	36 pF [C1825C360KBGAC TU]	360 pF [C1825C361KBGAC TU]
330 uF [T530X337M010AT E004]	3554BM  3554SM	36 pF [C2220C360KBGAC TU]	360 pF [C2220C361KBGAC TU]
330 uF [T530X337M010AT E005]	35CGQ045  35CGQ100	36 pF [C2220C360KZGACT U]	360 pF [C2225C361KBGAC TU]
330 uF [T530X337M010AT E006]	35CGQ150  35CLQ045	36 pF [C2225C360KBGAC TU]	3-644456-5  3-644456-8
	35GQ100		

# Multisim 14.0 Education Components

---

39 mF [C0805C399KBGAC TU]	39 nF [C0805C393K4RACT U]	39 nF [C1206C393M1UAC TU]	39 pF [C0402C390K8GACT U]
39 nF [C0402C393K4RACT U]	39 nF [C0805C393K5RACT U]	39 nF [C1210C393K1RACT U]	39 pF [C0603C390K2GACT U]
39 nF [C0402C393K8RACT U]	39 nF [C0805C393K8RACT U]	39 nF [C1210C393K2RACT U]	39 pF [C0603C390K5GACT U]
39 nF [C0402C393K9RACT U]	39 nF [C0805F393K1RACT U]	39 nF [C1210C393K5RACT U]	39 pF [C0805C390K1GACT U]
39 nF [C0603C393K1RACT U]	39 nF [C0805F393K3RACT U]	39 nF [C1210C393KARACT U]	39 pF [C0805C390K2GACT U]
39 nF [C0603C393K3RACT U]	39 nF [C0805F393K4RACT U]	39 nF [C1812C393K1RACT U]	39 pF [C0805C390K5GACT U]
39 nF [C0603C393K4RACT U]	39 nF [C0805F393K5RACT U]	39 nF [C1812C393K5RACT U]	39 pF [C0805C390KBGAC TU]
39 nF [C0603C393K5RACT U]	39 nF [C1206C393K1RACT U]	39 nF [C2220C393K2GACT U]	39 pF [C0805C390KCGAC TU]
39 nF [C0603C393K8RACT U]	39 nF [C1206C393K4RACT U]	39 pF [C0201C390K3GACT U]	39 pF [C1206C390K1GACT U]
39 nF [C0805C393K1RACT U]	39 nF [C1206C393K5RACT U]	39 pF [C0402C390K4GACT U]	39 pF [C1206C390K2GACT U]
39 nF [C0805C393K3RACT U]	39 nF [C1206C393KARACT U]	39 pF [C0402C390K5GACT U]	39 pF [C1206C390K5GACT U]

# Multisim 14.0 Education Components

---

39 pF [C1206C390KBGAC TU]	390 nF [C0603C394K9RACT U]	390 nF [C1206F394K4RACT U]	390 nF [C1812F394K2RACT U]
39 pF [C1210C390KBGAC TU]	390 nF [C0805C394K3RACT U]	390 nF [C1210C394K3RACT U]	390 nF [C1812F394K3RACT U]
39 pF [C1812C390KBGAC TU]	390 nF [C0805C394K4RACT U]	390 nF [C1210C394K5RACT U]	390 nF [C1812F394K5RACT U]
39 pF [C1825C390KBGAC TU]	390 nF [C0805C394K8RACT U]	390 nF [C1210F394K3RACT U]	390 nF [C1825C394K1RACT U]
39 pF [C2220C390KBGAC TU]	390 nF [C0805C394K9RACT U]	390 nF [C1210F394K4RACT U]	390 nF [C1825C394K2RACT U]
39 pF [C2225C390KBGAC TU]	390 nF [C1206C394K1RACT U]	390 nF [C1210F394K5RACT U]	390 nF [C1825C394K5RACT U]
39 pF [CA064C390K5GAC TU]	390 nF [C1206C394K3RACT U]	390 nF [C1812C394K1RACT U]	390 nF [C2225C394K1RACT U]
390 nF [C0603C394K4PACT U]	390 nF [C1206C394K4RACT U]	390 nF [C1812C394K5RACT U]	390 nF [C2225C394K2RACT U]
390 nF [C0603C394K4RACT U]	390 nF [C1206C394K5RACT U]	390 nF [C1812C394KARACT U]	390 pF [C0402C391K1HACT U]
390 nF [C0603C394K8PACT U]	390 nF [C1206C394K8RACT U]	390 nF [C1812C394M5UAC TU]	390 pF [C0402C391K3HACT U]
390 nF [C0603C394K8RACT U]	390 nF [C1206F394K3RACT U]	390 nF [C1812F394K1RACT U]	390 pF [C0402C391K3RACT U]

# Multisim 14.0 Education Components

---

390 pF [C0402C391K4RACT U]	390 pF [C0805C391K1RACT U]	390 pF [C1812C391KBGAC TU]	3LN01M-TL-E  3LN01M-TL-H  3LN01SS-TL-E 3LN01SS-TL-H 3LP01SS-TL-E 3LP01SS-TL-H 3LP01S-TL-E
390 pF [C0402C391K5HACT U]	390 pF [C0805C391K2GACT U]	390 pF [C1825C391KBGAC TU]	
390 pF [C0402C391K5RACT U]	390 pF [C0805C391K4RACT U]	390 pF [C2220C391KBGAC TU]	
390 pF [C0603C391K1RACT U]	390 pF [C0805C391K5GACT U]	390 pF [C2225C391KBGAC TU]	3N246 3N247
390 pF [C0603C391K2RACT U]	390 pF [C0805C391K5RACT U]	390 pF [CA064C391K5GAC TU]	3N248 3N249
390 pF [C0603C391K3GACT U]	390 pF [C1206C391K1GACT U]	390 uF [A700X397M002AT E010]	3N250 3N251
390 pF [C0603C391K3RACT U]	390 pF [C1206C391K2GACT U]	390 uF [A700X397M002AT E015]	3N252 3N253
390 pF [C0603C391K4RACT U]	390 pF [C1206C391K5GACT U]	3BH41  3GH41	3N254 3N255 3N256
390 pF [C0603C391K5GACT U]	390 pF [C1206C391KBGAC TU]	3JH41  3KASMC15AHE3/57 T	3N257 3N258
390 pF [C0603C391K5RACT U]	390 pF [C1206C391KCGAC TU]	3KASMC24AHE3/9A T	3N259 3P1S
390 pF [C0805C391K1GACT U]	390 pF [C1210C391KBGAC TU]	3KASMC28AHM3/5 7T	3P2S 3P3S
		3Line_Bussed  3Line_Isolated	3P4S

# Multisim 14.0 Education Components

---

3P5S	4.3 nF [C2225C432KBGAC TU]	4.7 nF [C0603C472K4RACT U]	4.7 nF [C0805C472K3RACT U]
3PDT_DB			
3PDT_SB	4.7 nF [C0402C472K3RACT U]	4.7 nF [C0603C472K5HACT U]	4.7 nF [C0805C472K4RACT U]
3PST_DB			
3PST_SB	4.7 nF [C0402C472K4RACT U]	4.7 nF [C0603C472K5RACT U]	4.7 nF [C0805C472K5HACT U]
4.3 nF [C0603C432K1HACT U]	4.7 nF [C0402C472K5RACT U]	4.7 nF [C0603C472K8RACT U]	4.7 nF [C0805C472K5RACT U]
4.3 nF [C0603C432K3HACT U]	4.7 nF [C0402C472K8RACT U]	4.7 nF [C0603C472K9RACT U]	4.7 nF [C0805C472KARACT U]
4.3 nF [C0603C432K5HACT U]	4.7 nF [C0402C472K9RACT U]	4.7 nF [C0805C472K1GACT U]	4.7 nF [C1206C472K1RACT U]
4.3 nF [C0805C432K1GACT U]	4.7 nF [C0603C472K1HACT U]	4.7 nF [C0805C472K1HACT U]	4.7 nF [C1206C472K2RACT U]
4.3 nF [C0805C432K1HACT U]	4.7 nF [C0603C472K1RACT U]	4.7 nF [C0805C472K1RACT U]	4.7 nF [C1206C472K3RACT U]
4.3 nF [C0805C432K3HACT U]	4.7 nF [C0603C472K3GACT U]	4.7 nF [C0805C472K2RACT U]	4.7 nF [C1206C472K4GACT U]
4.3 nF [C0805C432K5HACT U]	4.7 nF [C0603C472K3HACT U]	4.7 nF [C0805C472K3GACT U]	4.7 nF [C1206C472K5GACT U]
4.3 nF [C1825C432KBGAC TU]	4.7 nF [C0603C472K3RACT U]	4.7 nF [C0805C472K3HACT U]	4.7 nF [C1206C472K5RACT U]
4.3 nF [C2220C432KBGAC TU]			

# Multisim 14.0 Education Components

---

4.7 nF [C1210C472K1GACT U]	4.7 nF [C2225C472K2GACT U]	4.7 uF [C1206C475K3RACT U]	4.7 uF [C1210C475K3RACT U]
4.7 nF [C1210C472K1RACT U]	4.7 nF [C2225C472KBGAC TU]	4.7 uF [C1206C475K4PACT U]	4.7 uF [C1210C475K4PACT U]
4.7 nF [C1210C472K2RACT U]	4.7 nF [CA064C472K3RACT U]	4.7 uF [C1206C475K4RACT U]	4.7 uF [C1210C475K4RACT U]
4.7 nF [C1210C472K5GACT U]	4.7 nF [CA064C472K5RACT U]	4.7 uF [C1206C475K5PACT U]	4.7 uF [C1210C475K5R1C7 186]
4.7 nF [C1210C472K5RACT U]	4.7 uF [C0603C475K8PACT U]	4.7 uF [C1206C475K8NAC TU]	4.7 uF [C1210C475K5RACT U]
4.7 nF [C1812C472K1GACT U]	4.7 uF [C0603C475K9PACT U]	4.7 uF [C1206C475K8PACT U]	4.7 uF [C1210C475K8PACT U]
4.7 nF [C1812C472K2GACT U]	4.7 uF [C0805C475K3PACT U]	4.7 uF [C1206C475K8RACT U]	4.7 uF [C1210C475K8RACT U]
4.7 nF [C1812C472K5GACT U]	4.7 uF [C0805C475K4PACT U]	4.7 uF [C1206C475K9PACT U]	4.7 uF [C1210C475K9PACT U]
4.7 nF [C1825C472K2GACT U]	4.7 uF [C0805C475K8PACT U]	4.7 uF [C1206C475K9RACT U]	4.7 uF [C1210C475K9RACT U]
4.7 nF [C1825C472KBGAC TU]	4.7 uF [C0805C475K9PACT U]	4.7 uF [C1210C475K3NAC TU]	4.7 uF [C1210C475M4VAC TU]
4.7 nF [C2220C472KBGAC TU]	4.7 uF [C1206C475K3PACT U]	4.7 uF [C1210C475K3PACT U]	4.7 uF [C1210C475M8VAC TU]



# Multisim 14.0 Education Components

---

4.7 uF [T409D475M010AH 4250]	4.7 uF [T491D475M035AT ]	4.7 uF [T494C475M020AT]	4.7 uF [T495D475M050AT E275]
4.7 uF [T429C475M006AH 4250]	4.7 uF [T491D475M050AT ]	4.7 uF [T494C475M025AT]	4.7 uF [T495D475M050AT E300]
4.7 uF [T491A475M004AT]	4.7 uF [T491S475M006AT]	4.7 uF [T494D475M035AT ]	4.7 uF [T495X475M050AT E300]
4.7 uF [T491A475M006AT]	4.7 uF [T491S475M010AT]	4.7 uF [T494D475M050AT ]	4.7 uF [T498A475M010AT E2K9]
4.7 uF [T491A475M010AT]	4.7 uF [T491T475M016AT]	4.7 uF [T494S475M006AT]	4.7 uF [T498B475M010AT E2K7]
4.7 uF [T491A475M016AT]	4.7 uF [T494A475M004AT]	4.7 uF [T494S475M010AT]	4.7 uF [T498B475M016AT E2K1]
4.7 uF [T491A475M020AT]	4.7 uF [T494A475M006AT]	4.7 uF [T494T475M016AT]	4.7 uF [T521D475M063AT E075]
4.7 uF [T491A475M025AT]	4.7 uF [T494A475M010AT]	4.7 uF [T495A475M010AT E1K3]	4.7 uF [T521D475M063AT E300]
4.7 uF [T491B475M010AT]	4.7 uF [T494A475M016AT]	4.7 uF [T495B475M016AT E700]	4.7 uF [T540D475M063AH 6510]
4.7 uF [T491B475M016AT]	4.7 uF [T494A475M020AT]	4.7 uF [T495C475M035AT E450]	4_AMP
4.7 uF [T491B475M020AT]	4.7 uF [T494A475M025AT]	4.7 uF [T495C475M035AT E500]	40_AMP
4.7 uF [T491B475M025AT]	4.7 uF [T494B475M010AT]	4.7 uF [T495C475M035AT E600]	4000BD_10V
4.7 uF [T491C475M020AT]	4.7 uF [T494B475M016AT]		4000BD_15V
4.7 uF [T491C475M025AT]	4.7 uF [T494B475M020AT]		4000BD_5V
4.7 uF [T491C475M035AT]	4.7 uF [T494B475M025AT]		

# Multisim 14.0 Education Components

---

4000BP_10V	4002BT_15V	40106BP_10V	4011BP_5V
4000BP_15V	4002BT_5V	40106BP_15V	4011BP_5V
4000BP_5V	4008BD_10V	40106BP_5V	4011BT_10V
4000BP_5V	4008BD_15V	40106BP_5V	4011BT_15V
4000BT_10V	4008BD_5V	40106BT_10V	4011BT_5V
4000BT_15V	4008BP_10V	40106BT_15V	4012BD_10V
4000BT_5V	4008BP_15V	40106BT_5V	4012BD_15V
4001BD_10V	4008BP_5V	4010BC1_10V	4012BD_5V
4001BD_15V	4008BP_5V	4010BC1_15V	4012BP_10V
4001BD_5V	4008BT_10V	4010BC1_5V	4012BP_15V
4001BP_10V	4008BT_15V	4010BEY_10V	4012BP_5V
4001BP_15V	4008BT_5V	4010BEY_15V	4012BP_5V
4001BP_5V	4009BCL_10V	4010BEY_5V	4012BT_10V
4001BP_5V	4009BCL_15V	4010BF_10V	4012BT_15V
4001BT_10V	4009BCL_5V	4010BF_15V	4012BT_5V
4001BT_15V	4009BCP_10V	4010BF_5V	4013BD_10V
4001BT_5V	4009BCP_15V	4010BF_5V	4013BD_15V
4002BD_10V	4009BCP_5V	4010BM1_10V	4013BD_5V
4002BD_15V	4009BCP_5V	4010BM1_15V	4013BP_10V
4002BD_5V	4009BD_10V	4010BM1_5V	4013BP_15V
4002BP_10V	4009BD_15V	4011BD_10V	4013BP_5V
4002BP_15V	4009BD_5V	4011BD_15V	4013BP_5V
4002BP_5V	40106BD_10V	4011BD_5V	4013BT_10V
4002BP_5V	40106BD_15V	4011BP_10V	4013BT_15V
4002BT_10V	40106BD_5V	4011BP_15V	4013BT_5V

# Multisim 14.0 Education Components

---

4014BD_10V	40160BP_5V	40163BP_10V	4017BD_15V
4014BD_15V	40160BT_10V	40163BP_15V	4017BD_5V
4014BD_5V	40160BT_15V	40163BP_5V	4017BP_10V
4014BP_10V	40160BT_5V	40163BT_10V	4017BP_10V
4014BP_15V	40161BD_10V	40163BT_15V	4017BP_15V
4014BP_5V	40161BD_15V	40163BT_5V	4017BP_5V
4014BP_5V	40161BD_5V	40174BD_10V	4017BP_5V
4014BT_10V	40161BP_10V	40174BD_15V	4017BT_10V
4014BT_15V	40161BP_15V	40174BD_5V	4017BT_15V
4014BT_5V	40161BP_5V	40174BP_10V	4017BT_5V
4015BD_10V	40161BT_10V	40174BP_15V	4018BD_10V
4015BD_15V	40161BT_15V	40174BP_5V	4018BD_15V
4015BD_5V	40161BT_5V	40174BT_10V	4018BD_5V
4015BP_10V	40162BD_10V	40174BT_15V	4018BP_10V
4015BP_15V	40162BD_15V	40174BT_5V	4018BP_15V
4015BP_5V	40162BD_5V	40175BD_10V	4018BP_5V
4015BP_5V	40162BP_10V	40175BD_15V	4018BT_10V
4015BT_10V	40162BP_15V	40175BD_5V	4018BT_15V
4015BT_15V	40162BP_5V	40175BP_10V	4018BT_5V
4015BT_5V	40162BT_10V	40175BP_15V	40192BD_10V
40160BD_10V	40162BT_15V	40175BP_5V	40192BD_15V
40160BD_15V	40162BT_5V	40175BT_10V	40192BD_5V
40160BD_5V	40163BD_10V	40175BT_15V	40192BP_10V
40160BP_10V	40163BD_15V	40175BT_5V	40192BP_15V
40160BP_15V	40163BD_5V	4017BD_10V	40192BP_5V

# Multisim 14.0 Education Components

---

40192BT_10V	40195BP_15V	4021BD_10V	40244BP_10V
40192BT_15V	40195BP_5V	4021BD_15V	40244BP_15V
40192BT_5V	40195BT_10V	4021BD_5V	40244BP_5V
40193BD_10V	40195BT_15V	4021BP_10V	40244BT_10V
40193BD_15V	40195BT_5V	4021BP_15V	40244BT_15V
40193BD_5V	4019BD_10V	4021BP_5V	40244BT_5V
40193BP_10V	4019BD_15V	4021BT_10V	40245BP_10V
40193BP_15V	4019BD_5V	4021BT_15V	40245BP_15V
40193BP_5V	4019BP_10V	4021BT_5V	40245BP_5V
40193BT_10V	4019BP_15V	4023BD_10V	40245BT_10V
40193BT_15V	4019BP_5V	4023BD_15V	40245BT_15V
40193BT_5V	4019BP_5V	4023BD_5V	40245BT_5V
40194BD_10V	4019BT_10V	4023BP_10V	4024BD_10V
40194BD_15V	4019BT_15V	4023BP_15V	4024BD_15V
40194BD_5V	4019BT_5V	4023BP_5V	4024BD_5V
40194BP_10V	4020BD_10V	4023BP_5V	4024BP_10V
40194BP_15V	4020BD_15V	4023BT_10V	4024BP_15V
40194BP_5V	4020BD_5V	4023BT_15V	4024BP_5V
40194BT_10V	4020BP_10V	4023BT_5V	4024BP_5V
40194BT_15V	4020BP_10V	40240BP_10V	4024BT_10V
40194BT_5V	4020BP_15V	40240BP_15V	4024BT_15V
40195BD_10V	4020BP_5V	40240BP_5V	4024BT_5V
40195BD_15V	4020BT_10V	40240BT_10V	4025BD_10V
40195BD_5V	4020BT_15V	40240BT_15V	4025BD_15V
40195BP_10V	4020BT_5V	40240BT_5V	4025BD_5V

# Multisim 14.0 Education Components

---

4025BP_10V	4028BT_15V	4032BCP_15V	40374BT_5V
4025BP_15V	4028BT_5V	4032BCP_5V	4038BCL_10V
4025BP_5V	4029BD_10V	4032BD_10V	4038BCL_15V
4025BP_5V	4029BD_15V	4032BD_15V	4038BCL_5V
4025BT_10V	4029BD_5V	4032BD_5V	4038BCP_10V
4025BT_15V	4029BP_10V	4035BD_10V	4038BCP_15V
4025BT_5V	4029BP_15V	4035BD_15V	4038BCP_5V
4027BD_10V	4029BP_5V	4035BD_5V	4038BD_10V
4027BD_15V	4029BT_10V	4035BP_10V	4038BD_15V
4027BD_5V	4029BT_15V	4035BP_15V	4038BD_5V
4027BP_10V	4029BT_5V	4035BP_5V	4040BD_10V
4027BP_15V	4030BD_10V	4035BT_10V	4040BD_15V
4027BP_5V	4030BD_15V	4035BT_15V	4040BD_5V
4027BP_5V	4030BD_5V	4035BT_5V	4040BP_10V
4027BT_10V	4030BP_10V	40373BP_10V	4040BP_15V
4027BT_15V	4030BP_15V	40373BP_15V	4040BP_5V
4027BT_5V	4030BP_5V	40373BP_5V	4040BP_5V
4028BD_10V	4030BP_5V	40373BT_10V	4040BT_10V
4028BD_15V	4030BT_10V	40373BT_15V	4040BT_15V
4028BD_5V	4030BT_15V	40373BT_5V	4040BT_5V
4028BP_10V	4030BT_5V	40374BP_10V	4041BD_10V
4028BP_15V	4032BCL_10V	40374BP_15V	4041BD_15V
4028BP_5V	4032BCL_15V	40374BP_5V	4041BD_5V
4028BP_5V	4032BCL_5V	40374BT_10V	4041BP_10V
4028BT_10V	4032BCP_10V	40374BT_15V	4041BP_15V

# Multisim 14.0 Education Components

---

4041BP_5V	4044BD_10V	4050BP_5V	4068BD_5V
4041BP_5V	4044BD_15V	4050BP_5V	4068BP_10V
4041BT_10V	4044BD_5V	4050BT_10V	4068BP_15V
4041BT_15V	4044BP_10V	4050BT_15V	4068BP_5V
4041BT_5V	4044BP_15V	4050BT_5V	4068BP_5V
4042BD_10V	4044BP_5V	4060BD_10V	4068BT_10V
4042BD_15V	4044BP_5V	4060BD_15V	4068BT_15V
4042BD_5V	4044BT_10V	4060BD_5V	4068BT_5V
4042BP_10V	4044BT_15V	4060BP_10V	4069BCL_10V
4042BP_15V	4044BT_5V	4060BP_15V	4069BCL_15V
4042BP_5V	4049BD_10V	4060BP_5V	4069BCL_5V
4042BP_5V	4049BD_15V	4060BT_10V	4069BCP_10V
4042BT_10V	4049BD_5V	4060BT_15V	4069BCP_15V
4042BT_15V	4049BP_10V	4060BT_5V	4069BCP_5V
4042BT_5V	4049BP_15V	4066BD_10V	4069BCP_5V
4043BD_10V	4049BP_5V	4066BD_15V	4069BD_10V
4043BD_15V	4049BP_5V	4066BD_5V	4069BD_15V
4043BD_5V	4049BT_10V	4066BP_10V	4069BD_5V
4043BP_10V	4049BT_15V	4066BP_15V	4070BD_10V
4043BP_15V	4049BT_5V	4066BP_5V	4070BD_15V
4043BP_5V	4050BD_10V	4066BT_10V	4070BD_5V
4043BP_5V	4050BD_15V	4066BT_15V	4070BP_10V
4043BT_10V	4050BD_5V	4066BT_5V	4070BP_15V
4043BT_15V	4050BP_10V	4068BD_10V	4070BP_5V
4043BT_5V	4050BP_15V	4068BD_15V	4070BP_5V

# Multisim 14.0 Education Components

---

4070BT_10V	4073BD_5V	4076BT_10V	4081BD_5V
4070BT_15V	4073BP_10V	4076BT_15V	4081BP_10V
4070BT_5V	4073BP_15V	4076BT_5V	4081BP_15V
4071BD_10V	4073BP_5V	4077BD_10V	4081BP_5V
4071BD_15V	4073BP_5V	4077BD_15V	4081BP_5V
4071BD_5V	4073BT_10V	4077BD_5V	4081BT_10V
4071BP_10V	4073BT_15V	4077BP_10V	4081BT_15V
4071BP_15V	4073BT_5V	4077BP_15V	4081BT_5V
4071BP_5V	4075BD_10V	4077BP_5V	4082BD_10V
4071BP_5V	4075BD_15V	4077BP_5V	4082BD_15V
4071BT_10V	4075BD_5V	4077BT_10V	4082BD_5V
4071BT_15V	4075BP_10V	4077BT_15V	4082BP_10V
4071BT_5V	4075BP_15V	4077BT_5V	4082BP_15V
4072BD_10V	4075BP_5V	4078BD_10V	4082BP_5V
4072BD_15V	4075BP_5V	4078BD_15V	4082BP_5V
4072BD_5V	4075BT_10V	4078BD_5V	4082BT_10V
4072BP_10V	4075BT_15V	4078BP_10V	4082BT_15V
4072BP_15V	4075BT_5V	4078BP_15V	4082BT_5V
4072BP_5V	4076BD_10V	4078BP_5V	4085BD_10V
4072BP_5V	4076BD_15V	4078BP_5V	4085BD_15V
4072BT_10V	4076BD_5V	4078BT_10V	4085BD_5V
4072BT_15V	4076BD_5V	4078BT_15V	4085BP_10V
4072BT_5V	4076BP_10V	4078BT_5V	4085BP_15V
4073BD_10V	4076BP_15V	4081BD_10V	4085BP_5V
4073BD_15V	4076BP_5V	4081BD_15V	4085BP_5V

# Multisim 14.0 Education Components

---

4085BT_10V	4094BD_5V	43 pF [C1206C430KBGAC TU]	430 pF [C0603C431K5HACT U]
4085BT_15V	4094BP_10V		
4085BT_5V	4094BP_15V	43 pF [C1210C430KBGAC TU]	430 pF [C1206C431KBGAC TU]
4086BD_10V	4094BP_5V		
4086BD_15V	4094BT_10V	43 pF [C1812C430KBGAC TU]	430 pF [C1210C431KBGAC TU]
4086BD_5V	4094BT_15V		
4086BD_5V	4094BT_5V		
4086BP_10V	4099BCL_10V	43 pF [C1825C430KBGAC TU]	430 pF [C1812C431KBGAC TU]
4086BP_15V	4099BCL_15V		
4086BP_5V	4099BCL_5V	43 pF [C2220C430KBGAC TU]	430 pF [C1825C431KBGAC TU]
4086BT_10V	4099BCP_10V		
4086BT_15V	4099BCP_15V	43 pF [C2225C430KBGAC TU]	430 pF [C2220C431KBGAC TU]
4086BT_5V	4099BCP_5V		
4093BD_10V	4099BDW_10V	430 pF [C0402C431K1HACT U]	430 pF [C2225C431KBGAC TU]
4093BD_15V	4099BDW_15V		
4093BD_5V	4099BDW_5V	430 pF [C0402C431K3HACT U]	4502BD_10V 4502BD_15V 4502BD_5V
4093BP_10V	40EPS08		
4093BP_15V	40EPS12		
4093BP_5V	40EPS16	430 pF [C0402C431K5HACT U]	4502BP_10V 4502BP_15V
4093BP_5V	413990-1		
4093BT_10V	43 mF [C0805C439KBGAC TU]	430 pF [C0603C431K1HACT U]	4502BP_5V 4502BP_5V
4093BT_15V			
4093BT_5V	43 pF [C0805C430KBGAC TU]	430 pF [C0603C431K3HACT U]	4502BT_10V 4502BT_15V
4094BD_10V			
4094BD_15V			



# Multisim 14.0 Education Components

---

4502BT_5V	4510BP_15V	4512BT_5V	4516BP_15V
4503BCL_10V	4510BP_5V	4514BD_10V	4516BP_5V
4503BCL_15V	4510BP_5V	4514BD_15V	4516BP_5V
4503BCL_5V	4510BT_10V	4514BD_5V	4516BT_10V
4503BCP_10V	4510BT_15V	4514BP_10V	4516BT_15V
4503BCP_15V	4510BT_5V	4514BP_15V	4516BT_5V
4503BCP_5V	4511BD_10V	4514BP_5V	4518BD_10V
4503BCP_5V	4511BD_15V	4514BP_5V	4518BD_15V
4503BD_10V	4511BD_5V	4514BT_10V	4518BD_5V
4503BD_15V	4511BP_10V	4514BT_15V	4518BP_10V
4503BD_5V	4511BP_15V	4514BT_5V	4518BP_15V
4508BD_10V	4511BP_5V	4515BD_10V	4518BP_5V
4508BD_15V	4511BP_5V	4515BD_15V	4518BP_5V
4508BD_5V	4511BT_10V	4515BD_5V	4518BT_10V
4508BP_10V	4511BT_15V	4515BP_10V	4518BT_15V
4508BP_15V	4511BT_5V	4515BP_15V	4518BT_5V
4508BP_5V	4512BD_10V	4515BP_5V	4519BD_10V
4508BP_5V	4512BD_15V	4515BP_5V	4519BD_15V
4508BT_10V	4512BD_5V	4515BT_10V	4519BD_5V
4508BT_15V	4512BP_10V	4515BT_15V	4519BP_10V
4508BT_5V	4512BP_15V	4515BT_5V	4519BP_15V
4510BD_10V	4512BP_5V	4516BD_10V	4519BP_5V
4510BD_15V	4512BP_5V	4516BD_15V	4519BT_10V
4510BD_5V	4512BT_10V	4516BD_5V	4519BT_15V
4510BP_10V	4512BT_15V	4516BP_10V	4519BT_5V

# Multisim 14.0 Education Components

---

4520BD_10V	4526BT_10V	4539BP_10V	4555BP_15V
4520BD_15V	4526BT_15V	4539BP_15V	4555BP_5V
4520BD_5V	4526BT_5V	4539BP_5V	4555BT_10V
4520BP_10V	4531BD_10V	4539BT_10V	4555BT_15V
4520BP_15V	4531BD_15V	4539BT_15V	4555BT_5V
4520BP_5V	4531BD_5V	4539BT_5V	4556BD_10V
4520BP_5V	4531BP_10V	4543BD_10V	4556BD_15V
4520BT_10V	4531BP_15V	4543BD_15V	4556BD_5V
4520BT_15V	4531BP_5V	4543BD_5V	4556BP_10V
4520BT_5V	4531BT_10V	4543BP_10V	4556BP_15V
4522BD_10V	4531BT_15V	4543BP_15V	4556BP_5V
4522BD_15V	4531BT_5V	4543BP_5V	4556BP_5V
4522BD_5V	4532BD_10V	4543BT_10V	4556BT_10V
4522BP_10V	4532BD_15V	4543BT_15V	4556BT_15V
4522BP_15V	4532BD_5V	4543BT_5V	4556BT_5V
4522BP_5V	4532BP_10V	4544BCL_10V	4585BD_10V
4522BT_10V	4532BP_15V	4544BCL_15V	4585BD_15V
4522BT_15V	4532BP_5V	4544BCL_5V	4585BD_5V
4522BT_5V	4532BP_5V	4544BCP_10V	4585BP_10V
4526BD_10V	4532BT_10V	4544BCP_15V	4585BP_15V
4526BD_15V	4532BT_15V	4544BCP_5V	4585BP_5V
4526BD_5V	4532BT_5V	4555BD_10V	4585BT_10V
4526BP_10V	4539BD_10V	4555BD_15V	4585BT_15V
4526BP_15V	4539BD_15V	4555BD_5V	4585BT_5V
4526BP_5V	4539BD_5V	4555BP_10V	45970-4185

# Multisim 14.0 Education Components

---

4-644456-0	47 nF [C0603C473K3NAC TU]	47 nF [C0805C473K8RACT U]	47 nF [C1206C473K4RACT U]
46765-1001			
46765-2001	47 nF [C0603C473K3RACT U]	47 nF [C0805C473M5UAC TU]	47 nF [C1206C473K5HACT U]
47 mF [C0805C479KBGAC TU]	47 nF [C0603C473K4RACT U]	47 nF [C0805C473M5VAC TU]	47 nF [C1206C473K5RACT U]
47 mF [C1206C479K1GACT U]	47 nF [C0603C473K5NAC TU]	47 nF [C0805F473K3RACT U]	47 nF [C1206C473KARACT U]
47 nF [C0402C473K3RACT U]	47 nF [C0603C473K5RACT U]	47 nF [C0805F473K4RACT U]	47 nF [C1206C473M5UAC TU]
47 nF [C0402C473K4PACT U]	47 nF [C0603C473K8RACT U]	47 nF [C0805F473K5RACT U]	47 nF [C1206F473K1RACT U]
47 nF [C0402C473K4RACT U]	47 nF [C0603C473M3VAC TU]	47 nF [C1206C473K1HACT U]	47 nF [C1206F473K3RACT U]
47 nF [C0402C473K8PACT U]	47 nF [C0805C473K1RACT U]	47 nF [C1206C473K1RACT U]	47 nF [C1206F473K4RACT U]
47 nF [C0402C473K8RACT U]	47 nF [C0805C473K3RACT U]	47 nF [C1206C473K3GACT U]	47 nF [C1206F473K5RACT U]
47 nF [C0402C473K9PACT U]	47 nF [C0805C473K4RACT U]	47 nF [C1206C473K3HACT U]	47 nF [C1210C473K1GACT U]
47 nF [C0402C473K9RACT U]	47 nF [C0805C473K5RACT U]	47 nF [C1206C473K3RACT U]	47 nF [C1210C473K1HACT U]
47 nF [C0603C473K1RACT U]			

# Multisim 14.0 Education Components

---

47 nF [C1210C473K1RACT U]	47 nF [C1812C473K2RACT U]	47 pF [C0402C470K3GACT U]	47 pF [C0805C470KBGAC TU]
47 nF [C1210C473K2RACT U]	47 nF [C1812C473K5GACT U]	47 pF [C0402C470K4GACT U]	47 pF [C0805C470KCGAC TU]
47 nF [C1210C473K3GACT U]	47 nF [C1812C473K5HACT U]	47 pF [C0402C470K5GACT U]	47 pF [C1206C470K1GACT U]
47 nF [C1210C473K3HACT U]	47 nF [C1812C473K5RACT U]	47 pF [C0402C470K8GACT U]	47 pF [C1206C470K2GACT U]
47 nF [C1210C473K5GACT U]	47 nF [C1825C473K5RACT U]	47 pF [C0603C470K1GACT U]	47 pF [C1206C470K3GACT U]
47 nF [C1210C473K5HACT U]	47 nF [C2220C473K1GACT U]	47 pF [C0603C470K5GACT U]	47 pF [C1206C470K5GACT U]
47 nF [C1210C473K5RACT U]	47 nF [C2220C473K2GACT U]	47 pF [C0603C470K8GACT U]	47 pF [C1206C470KBGAC TU]
47 nF [C1210C473KARACT U]	47 nF [C2220C473K5GACT U]	47 pF [C0805C470K1GACT U]	47 pF [C1206C470KDGAC TU]
47 nF [C1812C473K1GACT U]	47 nF [CA064C473K4RACT U]	47 pF [C0805C470K2GACT U]	47 pF [C1206C470KFGACT U]
47 nF [C1812C473K1HACT U]	47 nF [CA064C473K8RACT U]	47 pF [C0805C470K3GACT U]	47 pF [C1206C470KGGAC TU]
47 nF [C1812C473K1RACT U]	47 pF [C0201C470K3GACT U]	47 pF [C0805C470K5GACT U]	47 pF [C1210C470K5GACT U]

# Multisim 14.0 Education Components

---

47 pF [C1210C470KBGAC TU]	47 uF [A700V476M006AT E028]	47 uF [T491D476M010AT ]	47 uF [T491X476M035AT]
47 pF [C1812C470KBGAC TU]	47 uF [T409H476M010AH 4250]	47 uF [T491D476M016AT ]	47 uF [T494A476M004AT]
47 pF [C1812C470KDGAC TU]	47 uF [T419F476M010AH 4250]	47 uF [T491D476M020AT ]	47 uF [T494B476M004AT]
47 pF [C1825C470KBGAC TU]	47 uF [T491A476M004AT]	47 uF [T491D476M025AT ]	47 uF [T494B476M006AT]
47 pF [C2220C470KBGAC TU]	47 uF [T491A476M006AT]	47 uF [T491E476M035AT]	47 uF [T494B476M010AT]
47 pF [C2225C470KBGAC TU]	47 uF [T491B476M004AT]	47 uF [T491T476M004AT]	47 uF [T494C476M004AT]
47 pF [CA064C470K3GAC TU]	47 uF [T491B476M006AT]	47 uF [T491T476M006AT]	47 uF [T494C476M006AT]
47 pF [CA064C470K5GAC TU]	47 uF [T491B476M010AT]	47 uF [T491U476M004AT ]	47 uF [T494C476M010AT]
47 pF [CA064C470K8GAC TU]	47 uF [T491C476M004AT]	47 uF [T491U476M006AT ]	47 uF [T494C476M016AT]
47 pF [CA064C470K8GAC TU]	47 uF [T491C476M010AT]	47 uF [T491U476M010AT ]	47 uF [T494D476M006AT ]
47 uF [A700V476M006AT E018]	47 uF [T491C476M016AT]	47 uF [T491V476M010AT]	47 uF [T494D476M010AT ]
47 uF [A700V476M006AT E025]	47 uF [T491C476M020AT]	47 uF [T491V476M016AT]	47 uF [T494D476M016AT ]
	47 uF [T491D476M006AT ]	47 uF [T491X476M025AT]	

# Multisim 14.0 Education Components

---

47 uF [T494D476M020AT ]	47 uF [T495B476M010AT E500]	47 uF [T495D476M025AT E250]	47 uF [T495X476M035AT E300]
47 uF [T494D476M025AT ]	47 uF [T495C476M016AT E350]	47 uF [T495V476M006AT E150]	47 uF [T497G476M006AT 6110]
47 uF [T494E476M035AT]	47 uF [T495D476M010AT E080]	47 uF [T495X476M020AT E065]	47 uF [T498C476M006AT E800]
47 uF [T494T476M004AT]	47 uF [T495D476M010AT E090]	47 uF [T495X476M020AT E100]	47 uF [T498D476M010AT E600]
47 uF [T494T476M006AT]	47 uF [T495D476M010AT E200]	47 uF [T495X476M020AT E150]	47 uF [T498D476M016AT E600]
47 uF [T494U476M004AT ]	47 uF [T495D476M016AT E080]	47 uF [T495X476M025AT E080]	47 uF [T510E476M035AT E050]
47 uF [T494U476M010AT ]	47 uF [T495D476M016AT E100]	47 uF [T495X476M025AT E150]	47 uF [T510X476M035AT E055]
47 uF [T494V476M010AT]	47 uF [T495D476M016AT E150]	47 uF [T495X476M025AT E185]	47 uF [T510X476M035AT E065]
47 uF [T494V476M016AT]	47 uF [T495D476M020AT E100]	47 uF [T495X476M025AT E200]	47 uF [T520A476M004AT E070]
47 uF [T494X476M025AT]	47 uF [T495D476M020AT E175]	47 uF [T495X476M035AT E185]	47 uF [T520A476M004AT E080]
47 uF [T494X476M035AT]	47 uF [T495D476M025AT E120]	47 uF [T495X476M035AT E200]	47 uF [T520A476M006AT E150]
47 uF [T495B476M006AT E450]			

# Multisim 14.0 Education Components

---

47 uF [T520A476M2R5AT E090]	47 uF [T520D476M016AT E070]	47 uF [T521X476M035AT E030]	470 nF [C0603C474K8PACT U]
47 uF [T520B476M006AT E025]	47 uF [T520Q476M011AT E040]	47 uF [T521X476M035AT E070]	470 nF [C0603C474K8RACT U]
47 uF [T520B476M006AT E035]	47 uF [T520T476M004AT E070]	47 uF [T525B476M006AT E080]	470 nF [C0603C474K9PACT U]
47 uF [T520B476M006AT E040]	47 uF [T520T476M006AT E040]	47 uF [T525D476M016AT E035]	470 nF [C0603C474K9RACT U]
47 uF [T520B476M006AT E070]	47 uF [T520T476M006AT E070]	47 uF [T525D476M016AT E065]	470 nF [C0805C474K3NAC TU]
47 uF [T520B476M008AT E035]	47 uF [T520V476M016AT E045]	47 uF [T525T476M006AT E080]	470 nF [C0805C474K3PACT U]
47 uF [T520B476M008AT E070]	47 uF [T520V476M016AT E070]	47 uF [T543A476M004AT E080]	470 nF [C0805C474K3RACT U]
47 uF [T520B476M010AT E035]	47 uF [T520W476M016AT E045]	47 uF [T543W476M016AT E045]	470 nF [C0805C474K4RACT U]
47 uF [T520B476M010AT E070]	47 uF [T521D476M020AT E055]	470 nF [C0402C474K9PACT U]	470 nF [C0805C474K8RACT U]
47 uF [T520C476M010AT E100]	47 uF [T521V476M020AT E090]	470 nF [C0603C474K4PACT U]	470 nF [C0805C474M3VAC TU]
47 uF [T520D476M016AT E035]	47 uF [T521W476M020AT E045]	470 nF [C0603C474K4RACT U]	470 nF [C0805C474M4VAC TU]

# Multisim 14.0 Education Components

---

470 nF [C1206C474K3NAC TU]	470 nF [C1210C474K4RACT U]	470 nF [C1812F474K3RACT U]	470 nF [C2225C474KARACT U]
470 nF [C1206C474K3RACT U]	470 nF [C1210C474K5RACT U]	470 nF [C1812F474K5RACT U]	470 nF [C2225C474M1UAC TU]
470 nF [C1206C474K4RACT U]	470 nF [C1210C474M5UAC TU]	470 nF [C1825C474K1RACT U]	470 nF [CDR06BX474AKSM ]
470 nF [C1206C474K5NAC TU]	470 nF [C1210F474K1RACT U]	470 nF [C1825C474K5RACT U]	470 nF [T491A474M025AT]
470 nF [C1206C474K5RACT U]	470 nF [C1210F474K3RACT U]	470 nF [C1825C474KARACT U]	470 nF [T491A474M035AT]
470 nF [C1206C474K8RACT U]	470 nF [C1210F474K4RACT U]	470 nF [C2220C474K1RACT U]	470 nF [T491B474M035AT]
470 nF [C1206C474M3VAC TU]	470 nF [C1210F474K5RACT U]	470 nF [C2220C474K5RACT U]	470 nF [T491C474M050AT]
470 nF [C1206C474M4VAC TU]	470 nF [C1812C474K5RACT U]	470 nF [C2220C474KARACT U]	470 nF [T494A474M025AT]
470 nF [C1206F474K3RACT U]	470 nF [C1812C474KARACT U]	470 nF [C2225C474K1RACT U]	470 nF [T494A474M035AT]
470 nF [C1206F474K4RACT U]	470 nF [C1812C474M5UAC TU]	470 nF [C2225C474K2RACT U]	470 nF [T494B474M035AT]
470 nF [C1210C474K3RACT U]	470 nF [C1812F474K1RACT U]	470 nF [C2225C474K5RACT U]	470 nF [T494C474M050AT]
			470 nF [T498A474M025AT E8K5]



# Multisim 14.0 Education Components

---

470 pF [C0402C471K1HACT U]	470 pF [C0603C471K2RACT U]	470 pF [C0805C471K2GACT U]	470 pF [C1206C471KCGAC TU]
470 pF [C0402C471K3GACT U]	470 pF [C0603C471K3GACT U]	470 pF [C0805C471K2RACT U]	470 pF [C1210C471K5GACT U]
470 pF [C0402C471K3HACT U]	470 pF [C0603C471K3HACT U]	470 pF [C0805C471K3RACT U]	470 pF [C1210C471KBGAC TU]
470 pF [C0402C471K3RACT U]	470 pF [C0603C471K3RACT U]	470 pF [C0805C471K4RACT U]	470 pF [C1210C471KCGAC TU]
470 pF [C0402C471K4RACT U]	470 pF [C0603C471K4RACT U]	470 pF [C0805C471K5GACT U]	470 pF [C1812C471K5GACT U]
470 pF [C0402C471K5HACT U]	470 pF [C0603C471K5GACT U]	470 pF [C0805C471K5RACT U]	470 pF [C1812C471KBGAC TU]
470 pF [C0402C471K5RACT U]	470 pF [C0603C471K5HACT U]	470 pF [C0805C471KARACT U]	470 pF [C1825C471KBGAC TU]
470 pF [C0402C471K8RACT U]	470 pF [C0603C471K5RACT U]	470 pF [C1206C471K1GACT U]	470 pF [C2220C471KBGAC TU]
470 pF [C0402C471K9RACT U]	470 pF [C0603C471K8RACT U]	470 pF [C1206C471K2GACT U]	470 pF [C2225C471KBGAC TU]
470 pF [C0603C471K1HACT U]	470 pF [C0805C471K1GACT U]	470 pF [C1206C471K5GACT U]	470 pF [CA064C471K4RACT U]
470 pF [C0603C471K1RACT U]	470 pF [C0805C471K1RACT U]	470 pF [C1206C471KBGAC TU]	470 pF [CA064C471K5GAC TU]

# Multisim 14.0 Education Components

---

470 pF [CA064C471K5RACT U]	470 uF [T494D477M004AT ]	470 uF [T495X477M004AT E045]	470 uF [T510X477M006AT E030]
470 pF [CA064C471K8RAC]	470 uF [T494D477M006AT ]	470 uF [T495X477M004AT E100]	470 uF [T513X477M006AH 6110]
470 uF [A700X477M002AT E007]	470 uF [T494E477M006AT]	470 uF [T495X477M006AT E030]	470 uF [T520C477M2R5AT E025]
470 uF [A700X477M002AT E010]	470 uF [T494E477M010AT]	470 uF [T495X477M006AT E045]	470 uF [T520C477M2R5AT E045]
470 uF [A700X477M002AT E015]	470 uF [T494X477M004AT]	470 uF [T495X477M006AT E050]	470 uF [T520D477M004AT E010]
470 uF [T489X477M006AT E200]	470 uF [T494X477M010AT]	470 uF [T495X477M006AT E065]	470 uF [T520D477M004AT E012]
470 uF [T491D477M004AT ]	470 uF [T495D477M006AT E045]	470 uF [T495X477M010AT E045]	470 uF [T520D477M004AT E015]
470 uF [T491D477M006AT ]	470 uF [T495D477M006AT E100]	470 uF [T495X477M010AT E050]	470 uF [T520D477M004AT E018]
470 uF [T491E477M006AT]	470 uF [T495D477M006AT E125]	470 uF [T495X477M010AT E060]	470 uF [T520D477M004AT E025]
470 uF [T491E477M010AT]	470 uF [T495E477M006AT E040]	470 uF [T495X477M010AT E100]	470 uF [T520D477M004AT E040]
470 uF [T491X477M004AT]	470 uF [T495X477M004AT E030]	470 uF [T495X477M010AT E200]	470 uF [T520D477M006AT E025]
470 uF [T491X477M010AT]			

# Multisim 14.0 Education Components

---

470 uF [T520D477M006AT E030]	470 uF [T520X477M006AT E010]	470 uF [T525D477M004AT E040]	470 uF [T530X477M006AT E010]
470 uF [T520D477M2R5AT E006]	470 uF [T520X477M006AT E018]	470 uF [T525D477M2R5AT E025]	470 uF [T530Y477M004AT E005]
470 uF [T520D477M2R5AT E007]	470 uF [T520X477M006AT E035]	470 uF [T528Z477M2R5AT E005]	470 uF [T530Y477M006AT E005]
470 uF [T520D477M2R5AT E009]	470 uF [T520X477M006AT E040]	470 uF [T528Z477M2R5AT E009]	470 uF [T543D477M2R5AT E007]
470 uF [T520V477M002AT E040]	470 uF [T520Y477M006AT E010]	470 uF [T528Z477M2R5AT E012]	47151-0001  47272-0001
470 uF [T520V477M2R5AT E007]	470 uF [T520Y477M006AT E015]	470 uF [T530D477M004AT E006]	4Line_Bussed  4Line_Isolated
470 uF [T520V477M2R5AT E009]	470 uF [T520Y477M006AT E018]	470 uF [T530D477M004AT E010]	4Line_Terminator  4P1S
470 uF [T520V477M2R5AT E012]	470 uF [T520Y477M006AT E025]	470 uF [T530D477M2R5AT E006]	4P2S  4P3S
470 uF [T520V477M2R5AT E015]	470 uF [T522Y477M006AT E040]	470 uF [T530X477M006AT E004]	4P4S  4P5S
470 uF [T520V477M2R5AT E018]	470 uF [T525D477M003AT E025]	470 uF [T530X477M006AT E005]	4POS_ROTARY  4V_0.5W
470 uF [T520W477M006AT E055]	470 uF [T525D477M004AT E025]	470 uF [T530X477M006AT E006]	5.1 nF [C0603C512K3HACT U]
			5.1 nF [C0603C512K5HACT U]

# Multisim 14.0 Education Components

---

5.1 nF [C0805C512K1GACT U]	5.6 nF [C0603C562K3GACT U]	5.6 nF [C0805C562K3GACT U]	5.6 nF [C1206C562KARACT U]
5.1 nF [C0805C512K1HACT U]	5.6 nF [C0603C562K3HACT U]	5.6 nF [C0805C562K3HACT U]	5.6 nF [C1210C562K5GACT U]
5.1 nF [C0805C512K3HACT U]	5.6 nF [C0603C562K3RACT U]	5.6 nF [C0805C562K3RACT U]	5.6 nF [C1210C562K5RACT U]
5.1 nF [C0805C512K5HACT U]	5.6 nF [C0603C562K4RACT U]	5.6 nF [C0805C562K4RACT U]	5.6 nF [C1210C562KARACT U]
5.1 nF [C1206C512K5GACT U]	5.6 nF [C0603C562K5HACT U]	5.6 nF [C0805C562K5HACT U]	5.6 nF [C1812C562K2GACT U]
5.1 nF [C2220C512KBGAC TU]	5.6 nF [C0603C562K5RACT U]	5.6 nF [C0805C562K5RACT U]	5.6 nF [C2220C562KBGAC TU]
5.1 nF [C2225C512KBGAC TU]	5.6 nF [C0603C562K8RACT U]	5.6 nF [C0805C562KARACT U]	5.6 nF [C2225C562KBGAC TU]
5.6 nF [C0402C562K3RACT U]	5.6 nF [C0805C562K1GACT U]	5.6 nF [C1206C562K1RACT U]	5.6 uF [C0805C565K9PACT U]
5.6 nF [C0402C562K4RACT U]	5.6 nF [C0805C562K1HACT U]	5.6 nF [C1206C562K2RACT U]	5.6 uF [C1206C565K4RACT U]
5.6 nF [C0402C562K5RACT U]	5.6 nF [C0805C562K1RACT U]	5.6 nF [C1206C562K5GACT U]	5.6 uF [C1206C565K8RACT U]
5.6 nF [C0603C562K1RACT U]	5.6 nF [C0805C562K2RACT U]	5.6 nF [C1206C562K5RACT U]	5.6 uF [C1206C565K9RACT U]

# Multisim 14.0 Education Components

---

5.6 uF [C1210C565K4PACT U]	51 pF [C0805C510KBGAC TU]	510 pF [C0402C511K5HACT U]	510 pF [C1825C511KBGAC TU]
5_AMP 50_AMP	51 pF [C0805C510KCGAC TU]	510 pF [C0603C511K1HACT U]	510 pF [C2220C511KBGAC TU]
50A02CH-TL-E 50A02CH-TL-H	51 pF [C1206C510K5GACT U]	510 pF [C0603C511K3HACT U]	510 pF [C2225C511KBGAC TU]
50C02CH-TL-E	51 pF [C1206C510KBGAC TU]	510 pF [C0603C511K5GACT U]	5103309-1 5103309-5
51 mF [C0805C519K3GACT U]	51 pF [C1210C510KBGAC TU]	510 pF [C0603C511K5HACT U]	5103309-6 5103309-7
51 mF [C0805C519KBGAC TU]	51 pF [C1812C510KBGAC TU]	510 pF [C0603C511K8GACT U]	5103309-8 5103310-1
51 pF [C0402C510K5GACT U]	51 pF [C1825C510KBGAC TU]	510 pF [C0805C511K5GACT U]	5103310-5 5103310-6
51 pF [C0603C510K2GACT U]	51 pF [C2220C510KBGAC TU]	510 pF [C1206C511K1GACT U]	5103310-7 5103310-8
51 pF [C0603C510K5GACT U]	51 pF [C2225C510KBGAC TU]	510 pF [C1206C511KBGAC TU]	5-1814400-1 5227222-3
51 pF [C0805C510K1GACT U]	510 pF [C0402C511K1HACT U]	510 pF [C1210C511KBGAC TU]	5227677-1 532903-2
51 pF [C0805C510K2GACT U]	510 pF [C0402C511K3HACT U]	510 pF [C1812C511KBGAC TU]	532903-6 534206-5
51 pF [C0805C510K5GACT U]			534237-3 534237-6

# Multisim 14.0 Education Components

---

534237-8	56 nF [C0805C563K2RACT U]	56 nF [C1206C563K5HACT U]	56 nF [C1210C563K2RACT U]
5414337-1			
555_Timer	56 nF [C0805C563K3RACT U]	56 nF [C1206C563K5RACT U]	56 nF [C1210C563K3HACT U]
555_TIMER_RATED			
555_VIRTUAL	56 nF [C0805C563K4RACT U]	56 nF [C1206C563KARACT U]	56 nF [C1210C563K5GACT U]
5558067-1			
56 mF [C0805C569KBGAC TU]	56 nF [C0805C563K5RACT U]	56 nF [C1206C563M5UAC TU]	56 nF [C1210C563K5HACT U]
56 nF [C0402C563K4RACT U]	56 nF [C0805C563K8RACT U]	56 nF [C1206F563K1RACT U]	56 nF [C1210C563K5RACT U]
56 nF [C0402C563K8RACT U]	56 nF [C0805F563K3RACT U]	56 nF [C1206F563K3RACT U]	56 nF [C1210C563KARACT U]
56 nF [C0402C563K9RACT U]	56 nF [C0805F563K4RACT U]	56 nF [C1206F563K4RACT U]	56 nF [C1812C563K1GACT U]
56 nF [C0603C563K3RACT U]	56 nF [C0805F563K5RACT U]	56 nF [C1206F563K5RACT U]	56 nF [C1812C563K1HACT U]
56 nF [C0603C563K4RACT U]	56 nF [C1206C563K1RACT U]	56 nF [C1210C563K1GACT U]	56 nF [C1812C563K1RACT U]
56 nF [C0603C563K5RACT U]	56 nF [C1206C563K3HACT U]	56 nF [C1210C563K1HACT U]	56 nF [C1812C563K5GACT U]
56 nF [C0805C563K1RACT U]	56 nF [C1206C563K3RACT U]	56 nF [C1210C563K1RACT U]	56 nF [C1812C563K5HACT U]

# Multisim 14.0 Education Components

---

56 nF [C2220C563K1GACT U]	56 pF [C0603C560K5GACT U]	56 pF [C1210C560KBGAC TU]	56 uF [A700V566M006AT E018]
56 nF [C2220C563K2GACT U]	56 pF [C0805C560K1GACT U]	56 pF [C1812C560KBGAC TU]	56 uF [A700V566M006AT E025]
56 nF [C2220C563K5GACT U]	56 pF [C0805C560K2GACT U]	56 pF [C1812C560KHGAC TU]	56 uF [A700V566M006AT E028]
56 pF [C0201C560K3GACT U]	56 pF [C0805C560K5GACT U]	56 pF [C1825C560KBGAC TU]	56 uF [T520T566M2R5AT E040]
56 pF [C0201C560K8GACT U]	56 pF [C0805C560KBGAC TU]	56 pF [C2220C560KBGAC TU]	56 uF [T520T566M2R5AT E070]
56 pF [C0402C560K3GACT U]	56 pF [C0805C560KDGAC TU]	56 pF [C2225C560KBGAC TU]	560 nF [C0603C564K8PACT U]
56 pF [C0402C560K5GACT U]	56 pF [C1206C560K1GACT U]	56 pF [CA064C560K5GAC TU]	560 nF [C0805C564K3RACT U]
56 pF [C0402C560K8GACT U]	56 pF [C1206C560K2GACT U]	56 uF [A700D566M008AT E015]	560 nF [C0805C564K4RACT U]
56 pF [C0603C560K1GACT U]	56 pF [C1206C560K5GACT U]	56 uF [A700D566M008AT E018]	560 nF [C0805C564K8RACT U]
56 pF [C0603C560K2GACT U]	56 pF [C1206C560KBGAC TU]	56 uF [A700D566M010AT E015]	560 nF [C1206C564K3RACT U]
56 pF [C0603C560K3GACT U]	56 pF [C1206C560KDGAC TU]	56 uF [A700D566M010AT E018]	560 nF [C1206C564K4RACT U]

# Multisim 14.0 Education Components

---

560 nF [C1206C564K5RACT U]	560 nF [C1825C564KARACT U]	560 pF [C0402C561K5HACT U]	560 pF [C0603C561K5RACT U]
560 nF [C1206F564K4RACT U]	560 nF [C2220C564K1RACT U]	560 pF [C0402C561K5RACT U]	560 pF [C0603C561K8RACT U]
560 nF [C1210C564K5RACT U]	560 nF [C2220C564K5RACT U]	560 pF [C0402C561K8RACT U]	560 pF [C0805C561K1GACT U]
560 nF [C1210F564K3RACT U]	560 nF [C2220C564KARACT U]	560 pF [C0603C561K1HACT U]	560 pF [C0805C561K1RACT U]
560 nF [C1210F564K4RACT U]	560 nF [C2225C564K5RACT U]	560 pF [C0603C561K1RACT U]	560 pF [C0805C561K2RACT U]
560 nF [C1210F564K5RACT U]	560 nF [C2225C564KARACT U]	560 pF [C0603C561K2RACT U]	560 pF [C0805C561K4RACT U]
560 nF [C1812C564K5RACT U]	560 pF [C0402C561K1HACT U]	560 pF [C0603C561K3HACT U]	560 pF [C0805C561K5GACT U]
560 nF [C1812F564K1RACT U]	560 pF [C0402C561K3GACT U]	560 pF [C0603C561K3RACT U]	560 pF [C0805C561K5RACT U]
560 nF [C1812F564K3RACT U]	560 pF [C0402C561K3HACT U]	560 pF [C0603C561K4RACT U]	560 pF [C0805C561K8RACT U]
560 nF [C1812F564K5RACT U]	560 pF [C0402C561K3RACT U]	560 pF [C0603C561K5GACT U]	560 pF [C1206C561K1GACT U]
560 nF [C1825C564K5RACT U]	560 pF [C0402C561K4RACT U]	560 pF [C0603C561K5HACT U]	560 pF [C1206C561K2GACT U]



# Multisim 14.0 Education Components

---

560 pF [C1206C561K5GACT U]	571-0500	5LN01SS-TL-E	6.2 nF [C0805C622K5HACT U]
560 pF [C1206C561KBGAC TU]	571-0600	5LN01SS-TL-H	6.2 nF [C2225C622KBGAC TU]
560 pF [C1210C561KBGAC TU]	571-0700	5LN01S-TL-E	6.8 nF [C0402C682K3RACT U]
560 pF [C1812C561KBGAC TU]	5AR4	5P1S	6.8 nF [C0402C682K4RACT U]
560 pF [C1825C561KBGAC TU]	5EQ100	5P2S	6.8 nF [C0402C682K5RACT U]
560 pF [C2220C561KBGAC TU]	5KP10A-E3/54	5P3S	6.8 nF [C0603C682K1RACT U]
560 pF [C2225C561KBGAC TU]	5KP16A-E3/54	5P4S	6.8 nF [C0603C682K2RACT U]
560 pF [CA064C561K2RACT U]	5KP18A-E3/54	5P5S	6.8 nF [C0603C682K3GACT U]
560 pF [T530D567M2R5AT E005]	5KP22A-E3/54	5POS_ROTARY	6.8 nF [C0603C682K3HACT U]
560 pF [T530D567M2R5AT E005]	5KP24A-E3/54	5U4GB	6.8 nF [C0603C682K3HACT U]
560 pF [T530D567M2R5AT E005]	5KP28A-E3/54	5V_1W	6.8 nF [C0603C682K3HACT U]
560 pF [T530D567M2R5AT E005]	5KP30A-E3/54	5V3A	6.8 nF [C0603C682K3HACT U]
560 pF [T530D567M2R5AT E005]	5KP33A-E3/54	5V4GA	6.8 nF [C0603C682K3HACT U]
560 pF [T530D567M2R5AT E005]	5KP40A-E3/54	5Y3GT	6.8 nF [C0603C682K3HACT U]
560 pF [T530D567M2R5AT E005]	5KP48A-E3/54	6.2 nF [C0805C622K1HACT U]	6.8 nF [C0603C682K3HACT U]
560 pF [T530D567M2R5AT E005]	5KP58A-E3/54	6.2 nF [C0805C622K1HACT U]	6.8 nF [C0603C682K3HACT U]
560 pF [T530D567M2R5AT E005]	5KP60A-E3/54	6.2 nF [C0805C622K1HACT U]	6.8 nF [C0603C682K3HACT U]
560 pF [T530D567M2R5AT E005]	5KP85A-E3/54	6.2 nF [C0805C622K1HACT U]	6.8 nF [C0603C682K3HACT U]
560 uF [T530D567M2R5AT E005]	5Line_Bussed	6.2 nF [C0805C622K1HACT U]	6.8 nF [C0603C682K3HACT U]
560 uF [T530D567M2R5AT E005]	5Line_Isolated	6.2 nF [C0805C622K1HACT U]	6.8 nF [C0603C682K3HACT U]
5687169-9	5LN01C-TB-E	6.2 nF [C0805C622K1HACT U]	6.8 nF [C0603C682K3HACT U]
571-0100	5LN01C-TB-H	6.2 nF [C0805C622K1HACT U]	6.8 nF [C0603C682K3HACT U]
571-0200	5LN01M-TL-E	6.2 nF [C0805C622K1HACT U]	6.8 nF [C0603C682K3HACT U]
571-0300	5LN01M-TL-H	6.2 nF [C0805C622K1HACT U]	6.8 nF [C0603C682K3HACT U]
571-0400	5LN01SP-AC	6.2 nF [C0805C622K1HACT U]	6.8 nF [C0603C682K3HACT U]

# Multisim 14.0 Education Components

---

6.8 nF [C0603C682K4RACT U]	6.8 nF [C0805C682K5GACT U]	6.8 nF [C1210C682K1RACT U]	6.8 uF [A700V685M016AT E070]
6.8 nF [C0603C682K5HACT U]	6.8 nF [C0805C682K5HACT U]	6.8 nF [C1210C682K5GACT U]	6.8 uF [C0805C685K8PACT U]
6.8 nF [C0603C682K5RACT U]	6.8 nF [C0805C682K5RACT U]	6.8 nF [C1210C682K5RACT U]	6.8 uF [C0805C685K9PACT U]
6.8 nF [C0603C682K8RACT U]	6.8 nF [C1206C682K1HACT U]	6.8 nF [C1210C682KARACT U]	6.8 uF [C1206C685K4PACT U]
6.8 nF [C0805C682K1GACT U]	6.8 nF [C1206C682K1RACT U]	6.8 nF [C1812C682K1GACT U]	6.8 uF [C1206C685K4RACT U]
6.8 nF [C0805C682K1HACT U]	6.8 nF [C1206C682K3GACT U]	6.8 nF [C1812C682K1RACT U]	6.8 uF [C1206C685K8RACT U]
6.8 nF [C0805C682K1RACT U]	6.8 nF [C1206C682K3HACT U]	6.8 nF [C1812C682K5GACT U]	6.8 uF [C1206C685K9PACT U]
6.8 nF [C0805C682K3GACT U]	6.8 nF [C1206C682K3RACT U]	6.8 nF [C1812C682K5RACT U]	6.8 uF [C1206C685K9RACT U]
6.8 nF [C0805C682K3HACT U]	6.8 nF [C1206C682K5HACT U]	6.8 nF [C2220C682K2GACT U]	6.8 uF [C1210C685K3PACT U]
6.8 nF [C0805C682K3RACT U]	6.8 nF [C1206C682K5RACT U]	6.8 nF [C2225C682KBGAC TU]	6.8 uF [C1210C685K4PACT U]
6.8 nF [C0805C682K4RACT U]	6.8 nF [C1210C682K1GACT U]	6.8 nF [CDR06BP682BKSM ]	6.8 uF [C1210C685K8PACT U]

# Multisim 14.0 Education Components

---

6.8 uF [C1210C685M4VAC TU]	6.8 uF [T491B685M025AT]	6.8 uF [T494A685M006AT]	6.8 uF [T494S685M004AT]
6.8 uF [T419B685M006AH 4250]	6.8 uF [T491C685M016AT]	6.8 uF [T494A685M010AT]	6.8 uF [T494S685M006AT]
6.8 uF [T419C685M010AH 4250]	6.8 uF [T491C685M020AT]	6.8 uF [T494A685M016AT]	6.8 uF [T494S685M010AT]
6.8 uF [T419C685M010AH 4250]	6.8 uF [T491C685M025AT]	6.8 uF [T494A685M020AT]	6.8 uF [T494T685M010AT]
6.8 uF [T429D685M006AH 4250]	6.8 uF [T491C685M035AT]	6.8 uF [T494B685M006AT]	6.8 uF [T494U685M020AT ]
6.8 uF [T489B685M010AT E3K0]	6.8 uF [T491D685M035AT ]	6.8 uF [T494B685M010AT]	6.8 uF [T494X685M050AT]
6.8 uF [T491A685M004AT]	6.8 uF [T491D685M050AT ]	6.8 uF [T494B685M016AT]	6.8 uF [T495C685M025AT E400]
6.8 uF [T491A685M006AT]	6.8 uF [T491S685M004AT]	6.8 uF [T494B685M025AT]	6.8 uF [T495C685M025AT E500]
6.8 uF [T491A685M010AT]	6.8 uF [T491S685M006AT]	6.8 uF [T494C685M016AT]	6.8 uF [T495D685M035AT E150]
6.8 uF [T491A685M016AT]	6.8 uF [T491S685M010AT]	6.8 uF [T494C685M020AT]	6.8 uF [T495D685M050AT E190]
6.8 uF [T491A685M020AT]	6.8 uF [T491T685M010AT]	6.8 uF [T494C685M025AT]	6.8 uF [T495D685M050AT E200]
6.8 uF [T491B685M006AT]	6.8 uF [T491U685M020AT ]	6.8 uF [T494C685M035AT]	6.8 uF [T495D685M050AT E300]
6.8 uF [T491B685M010AT]	6.8 uF [T491X685M050AT]	6.8 uF [T494D685M035AT ]	6.8 uF [T495D685M050AT E300]
6.8 uF [T491B685M016AT]	6.8 uF [T494A685M004AT]	6.8 uF [T494D685M050AT ]	

# Multisim 14.0 Education Components

---

6.8 uF [T497B685M010AT 6110]	62 pF [C0402C620K5GACT U]	620 pF [C0402C621K3HACT U]	620 pF [C2225C621KBGAC TU]
6.8 uF [T498A685M016AT E2K6]	62 pF [C0603C620K5GACT U]	620 pF [C0402C621K5HACT U]	640455-5 640455-8
6.8 uF [T498B685M016AT E1K8]	62 pF [C0805C620KBGAC TU]	620 pF [C0603C621K1HACT U]	68 mF [C0402C689K8GACT U]
6.8 uF [T498D685M035AT E900]	62 pF [C1206C620KBGAC TU]	620 pF [C0603C621K3HACT U]	68 mF [C0805C689KBGAC TU]
6.8 uF [T499C685M020AT E1K9]	62 pF [C1206C620KDGAC TU]	620 pF [C0603C621K5GACT U]	68 mF [C1206C689K2GACT U]
6.8 uF [T521D685M050AT E090]	62 pF [C1210C620KBGAC TU]	620 pF [C0603C621K5HACT U]	68 nF [C0402C683K4RACT U]
6.8 uF [T521V685M050AT E090]	62 pF [C1812C620KBGAC TU]	620 pF [C0805C621K5GACT U]	68 nF [C0402C683K8PACT U]
608PWM 60LQ045	62 pF [C1825C620KBGAC TU]	620 pF [C1210C621KBGAC TU]	68 nF [C0402C683K8RACT U]
60LQ100 61729-0010BLF	62 pF [C2220C620KBGAC TU]	620 pF [C1812C621KBGAC TU]	68 nF [C0402C683K9PACT U]
62 mF [C0805C629KBGAC TU]	62 pF [C2225C620KBGAC TU]	620 pF [C1825C621KBGAC TU]	68 nF [C0402C683K9RACT U]
62 pF [C0402C620K3GACT U]	620 pF [C0402C621K1HACT U]	620 pF [C2220C621KBGAC TU]	68 nF [C0603C683K3RACT U]

# Multisim 14.0 Education Components

---

68 nF [C0603C683K4RACT U]	68 nF [C0805F683K3RACT U]	68 nF [C1206F683K1RACT U]	68 nF [C1210C683K5HACT U]
68 nF [C0603C683K5RACT U]	68 nF [C0805F683K4RACT U]	68 nF [C1206F683K3RACT U]	68 nF [C1210C683K5RACT U]
68 nF [C0603C683K8RACT U]	68 nF [C0805F683K5RACT U]	68 nF [C1206F683K4RACT U]	68 nF [C1210C683KARACT U]
68 nF [C0603C683K9RACT U]	68 nF [C1206C683K1RACT U]	68 nF [C1206F683K5RACT U]	68 nF [C1210F683K2RACT U]
68 nF [C0603C683M3VAC TU]	68 nF [C1206C683K2RACT U]	68 nF [C1210C683K1GACT U]	68 nF [C1812C683K1GACT U]
68 nF [C0805C683K1RACT U]	68 nF [C1206C683K3GACT U]	68 nF [C1210C683K1HACT U]	68 nF [C1812C683K1HACT U]
68 nF [C0805C683K3RACT U]	68 nF [C1206C683K3HACT U]	68 nF [C1210C683K1RACT U]	68 nF [C1812C683K1RACT U]
68 nF [C0805C683K4RACT U]	68 nF [C1206C683K5HACT U]	68 nF [C1210C683K2RACT U]	68 nF [C1812C683K2RACT U]
68 nF [C0805C683K5RACT U]	68 nF [C1206C683K5RACT U]	68 nF [C1210C683K3GACT U]	68 nF [C1812C683K5GACT U]
68 nF [C0805C683K8RACT U]	68 nF [C1206C683KARACT U]	68 nF [C1210C683K3HACT U]	68 nF [C1812C683K5HACT U]
68 nF [C0805C683M5UAC TU]	68 nF [C1206C683M5UAC TU]	68 nF [C1210C683K5GACT U]	68 nF [C1812C683K5RACT U]

# Multisim 14.0 Education Components

---

68 nF [C2220C683K1GACT U]	68 pF [C0603C680K4GACT U]	68 pF [C1206C680KGGAC TU]	68 uF [A700D686M010AT E015]
68 nF [C2220C683K2GACT U]	68 pF [C0603C680K5GACT U]	68 pF [C1210C680KBGAC TU]	68 uF [A700D686M010AT E018]
68 nF [C2220C683K5GACT U]	68 pF [C0805C680K1GACT U]	68 pF [C1812C680KBGAC TU]	68 uF [A700V686M006AT E018]
68 nF [CA064C683K4RACT U]	68 pF [C0805C680K2GACT U]	68 pF [C1825C680KBGAC TU]	68 uF [A700V686M006AT E025]
68 nF [CDR05BX683BKSM ]	68 pF [C0805C680K5GACT U]	68 pF [C2220C680KBGAC TU]	68 uF [A700V686M006AT E028]
68 pF [C0201C680K3GACT U]	68 pF [C0805C680KBGAC TU]	68 pF [C2225C680KBGAC TU]	68 uF [T419G686M010AH 4250]
68 pF [C0402C680K3GACT U]	68 pF [C1206C680K1GACT U]	68 pF [CA064C680K5GAC TU]	68 uF [T491A686M004AT]
68 pF [C0402C680K5GACT U]	68 pF [C1206C680K2GACT U]	68 pF [CA064C680K8GAC TU]	68 uF [T491A686M006AT]
68 pF [C0402C680K8GACT U]	68 pF [C1206C680K5GACT U]	68 pF [CDR01BP680BKSM ]	68 uF [T491B686M006AT]
68 pF [C0603C680K2GACT U]	68 pF [C1206C680KBGAC TU]	68 uF [A700D686M008AT E015]	68 uF [T491B686M010AT]
68 pF [C0603C680K3GACT U]	68 pF [C1206C680KDGAC TU]	68 uF [A700D686M008AT E018]	68 uF [T491C686M004AT]

# Multisim 14.0 Education Components

---

68 uF [T491C686M010AT]	68 uF [T491V686M016AT]	68 uF [T494D686M010AT ]	68 uF [T495C686M010AT E225]
68 uF [T491C686M016AT]	68 uF [T491X686M020AT]	68 uF [T494D686M016AT ]	68 uF [T495D686M006AT E175]
68 uF [T491D686M004AT ]	68 uF [T491X686M025AT]	68 uF [T494D686M020AT ]	68 uF [T495D686M010AT E070]
68 uF [T491D686M006AT ]	68 uF [T494A686M004AT]	68 uF [T494D686M025AT ]	68 uF [T495D686M010AT E090]
68 uF [T491D686M010AT ]	68 uF [T494B686M004AT]	68 uF [T494U686M004AT ]	68 uF [T495D686M010AT E150]
68 uF [T491D686M016AT ]	68 uF [T494B686M006AT]	68 uF [T494U686M006AT ]	68 uF [T495D686M016AT E070]
68 uF [T491D686M020AT ]	68 uF [T494C686M004AT]	68 uF [T494U686M010AT ]	68 uF [T495D686M016AT E100]
68 uF [T491D686M025AT ]	68 uF [T494C686M006AT]	68 uF [T494V686M010AT]	68 uF [T495D686M016AT E150]
68 uF [T491U686M004AT ]	68 uF [T494C686M010AT]	68 uF [T494V686M016AT]	68 uF [T495D686M020AT E070]
68 uF [T491U686M006AT ]	68 uF [T494D686M004AT ]	68 uF [T494X686M020AT]	68 uF [T495D686M020AT E150]
68 uF [T491U686M010AT ]	68 uF [T494D686M006AT ]	68 uF [T495B686M010AT E900]	68 uF [T495D686M025AT E150]
68 uF [T491V686M010AT]			

# Multisim 14.0 Education Components

---

68 uF [T495D686M025AT E200]	68 uF [T520A686M2R5AT E080]	68 uF [T520T686M004AT E070]	68 uF [T520W686M010AT E040]
68 uF [T495V686M010AT E100]	68 uF [T520B686M004AT E025]	68 uF [T520T686M006AT E070]	68 uF [T521D686M016AT E050]
68 uF [T495V686M010AT E140]	68 uF [T520B686M004AT E035]	68 uF [T520T686M006AT E150]	68 uF [T521V686M016AT E050]
68 uF [T495V686M016AT E300]	68 uF [T520B686M004AT E040]	68 uF [T520U686M004AT E055]	68 uF [T521V686M016AT E090]
68 uF [T495X686M010AT E150]	68 uF [T520B686M004AT E070]	68 uF [T520U686M006AT E055]	68 uF [T525B686M004AT E080]
68 uF [T495X686M020AT E150]	68 uF [T520B686M006AT E025]	68 uF [T520U686M006AT E070]	68 uF [T525B686M006AT E080]
68 uF [T495X686M025AT E125]	68 uF [T520B686M006AT E035]	68 uF [T520V686M010AT E025]	68 uF [T525T686M004AT E080]
68 uF [T495X686M025AT E200]	68 uF [T520B686M006AT E040]	68 uF [T520V686M010AT E040]	68 uF [T543U686M006AT E055]
68 uF [T513X686M025AH 6110]	68 uF [T520B686M006AT E070]	68 uF [T520V686M010AT E045]	680 nF [C0603C684K4PACT U]
68 uF [T520A686M006AT E150]	68 uF [T520C686M006AT E100]	68 uF [T520V686M010AT E060]	680 nF [C0603C684K8PACT U]
68 uF [T520A686M2R5AT E070]	68 uF [T520C686M010AT E045]	68 uF [T520V686M010AT E100]	680 nF [C0805C684K3PACT U]



# Multisim 14.0 Education Components

---

680 nF [C0805C684K4RACT U]	680 nF [C1210C684K4RACT U]	680 nF [C1812F684K5RACT U]	680 nF [T491A684M035AT]
680 nF [C0805C684K8RACT U]	680 nF [C1210C684K5RACT U]	680 nF [C1825C684K1RACT U]	680 nF [T491B684M035AT]
680 nF [C0805C684M4VAC TU]	680 nF [C1210C684M3VAC TU]	680 nF [C1825C684K5RACT U]	680 nF [T491B684M050AT]
680 nF [C1206C684K3RACT U]	680 nF [C1210C684M5VAC TU]	680 nF [C1825C684KARACT U]	680 nF [T494A684M020AT]
680 nF [C1206C684K4RACT U]	680 nF [C1210F684K3RACT U]	680 nF [C2220C684K1RACT U]	680 nF [T494A684M025AT]
680 nF [C1206C684K5RACT U]	680 nF [C1210F684K4RACT U]	680 nF [C2220C684K5RACT U]	680 nF [T494A684M035AT]
680 nF [C1206C684K8RACT U]	680 nF [C1210F684K5RACT U]	680 nF [C2220C684KARACT U]	680 nF [T494B684M035AT]
680 nF [C1206C684M3VAC TU]	680 nF [C1812C684K5RACT U]	680 nF [C2225C684K1RACT U]	680 nF [T494B684M050AT]
680 nF [C1206C684M4VAC TU]	680 nF [C1812C684M5UAC TU]	680 nF [C2225C684K5RACT U]	680 nF [T494C684M050AT]
680 nF [C1206F684K4RACT U]	680 nF [C1812F684K1RACT U]	680 nF [C2225C684KARACT U]	680 nF [T496C684M050AT 6110]
680 nF [C1210C684K3RACT U]	680 nF [C1812F684K3RACT U]	680 nF [T491A684M020AT]	680 pF [C0402C681K1HACT U]
		680 nF [T491A684M025AT]	680 pF [C0402C681K3GACT U]

# Multisim 14.0 Education Components

---

680 pF [C0402C681K3RACT U]	680 pF [C0603C681K5GACT U]	680 pF [C1206C681K2GACT U]	680 uF [T491D687M004AT ]
680 pF [C0402C681K4RACT U]	680 pF [C0603C681K5HACT U]	680 pF [C1206C681K5GACT U]	680 uF [T491E687M006AT]
680 pF [C0402C681K5HACT U]	680 pF [C0603C681K5RACT U]	680 pF [C1206C681KCGAC TU]	680 uF [T491X687M004AT]
680 pF [C0402C681K5RACT U]	680 pF [C0805C681K1GACT U]	680 pF [C1210C681KBGAC TU]	680 uF [T494D687M004AT ]
680 pF [C0603C681K1HACT U]	680 pF [C0805C681K1RACT U]	680 pF [C1210C681KCGAC TU]	680 uF [T494X687M004AT]
680 pF [C0603C681K1RACT U]	680 pF [C0805C681K2RACT U]	680 pF [C1210C681KDGAC TU]	680 uF [T510E687M006AT E012]
680 pF [C0603C681K2RACT U]	680 pF [C0805C681K4GACT U]	680 pF [C1812C681KBGAC TU]	680 uF [T510E687M006AT E023]
680 pF [C0603C681K3GACT U]	680 pF [C0805C681K4RACT U]	680 pF [C1825C681KBGAC TU]	680 uF [T510X687M004AT E030]
680 pF [C0603C681K3HACT U]	680 pF [C0805C681K5GACT U]	680 pF [C2220C681KBGAC TU]	680 uF [T510X687M006AT E023]
680 pF [C0603C681K3RACT U]	680 pF [C0805C681K5RACT U]	680 pF [C2220C681KZGACT U]	680 uF [T513E687M006AH 6110]
680 pF [C0603C681K4RACT U]	680 pF [C1206C681K1GACT U]	680 pF [C2225C681KBGAC TU]	680 uF [T513E687M006AH 6120]

# Multisim 14.0 Education Components

---

680 uF [T513X687M004AH 6110]	680 uF [T520X687M004AT E010]	680 uF [T530D687M2R5AT E006]	6J5  6L6GC  6Line_Bussed  6Line_Isolated  6N1136  6N1136-X006  6N1136-X009T  6N136  6N136-000E  6N136-020E  6N136-060E  6N136-300E  6N136-320E  6N136-360E  6N136-X001  6N136-X006  6N136-X007T  6N136-X009T  6N136-X016  6N136-X017T  6N136-X019T  6N137  6N137-X006  6N137-X007T  6N139-000E
680 uF [T513X687M006AH 6110]	680 uF [T520X687M004AT E015]	680 uF [T530D687M2R5AT E010]	
680 uF [T513X687M006AH 6120]	680 uF [T520X687M004AT E035]	680 uF [T530X687M004AT E004]	
680 uF [T520D687M003AT E015]	680 uF [T520Y687M004AT E010]	680 uF [T530X687M004AT E006]	
680 uF [T520D687M003AT E040]	680 uF [T520Y687M004AT E015]	680 uF [T530X687M004AT E010]	
680 uF [T520D687M004AT E012]	680 uF [T520Y687M004AT E025]	680 uF [T530X687M006AT E010]	
680 uF [T520D687M004AT E015]	680 uF [T520Y687M2R5AT E015]	680 uF [T530X687M006AT E018]	
680 uF [T520D687M004AT E025]	680 uF [T520Y687M2R5AT E025]	680 uF [T530Y687M004AT E005]	
680 uF [T520D687M2R5AT E010]	680 uF [T525D687M003AT E025]	680 uF [T530Y687M2R5AT E006]	
680 uF [T520D687M2R5AT E015]	680 uF [T525D687M2R5AT E025]	680 uF [T543X687M004AT E015]	
680 uF [T520D687M2R5AT E040]	680 uF [T530D687M003AT E010]	690-009-521-900  6DJ8  6F6	

# Multisim 14.0 Education Components

---

6N139-020E	7.5 nF	7410N	74163N
6N139-060E	[C1206C752K1HACT U]	74116N	74164N
6N139-300E	7.5 nF	74125N	74165N
6N139-320E	[C1206C752K3HACT U]	74126N	74166N
6N139-360E	7.5 nF	7412N	7416N
6POS_ROTARY	[C1206C752K5HACT U]	74132N	74173N
6SF5		74136N	74174N
6SL7GT	7.5 nF	7413N	74175N
6SN7GTB	[CDR34BP752AKSM ]	74145N	7417N
6STEP_DECODER	73391-0060	74147N	74180N
6TQ045	7400N	74148N	74181J
6V6GTA	7401N	7414N	74181N
7.5 nF	7402N	74150N	74182J
[C0603C752K3HACT U]	7403N	74151N	74182N
7.5 nF	7404N	74152AJ	74190N
[C0805C752K1GACT U]	7405N	74152AN	74191N
	7406N	74153N	74192N
7.5 nF	7407N	74154N	74193N
[C0805C752K1HACT U]	7408J	74155N	74194N
7.5 nF	7408N	74156N	74195N
[C0805C752K3HACT U]	7409N	74157N	74198N
7.5 nF	74100J	74159N	74199N
[C0805C752K5GACT U]	74100N	74160N	741-DIV
7.5 nF	74107N	74161N	7420N
[C0805C752K5HACT U]	74109N	74162N	7422N

# Multisim 14.0 Education Components

---

74246N	7432N	7454N	74ALS05AM
74247N	7433N	7472N	74ALS05AN
74248J	74351N	7473N	74ALS08M
74248N	74365N	7474N	74ALS08N
74249J	74366N	7475N	74ALS09M
74249N	74367N	7476N	74ALS09N
74251J	74368N	7477W	74ALS109AM
74251N	7437N	7482J	74ALS109AN
74259N	7438N	7482N	74ALS10AM
7425N	74390N	7483N	74ALS10AN
7426N	74393N	7485N	74ALS11AM
74273DW	7439N	7486N	74ALS11AN
74273N	7440N	749070-9	74ALS125M
74279N	74425N	7490N	74ALS125N
7427N	74426N	7491N	74ALS133M
74283N	7442N	7492N	74ALS133N
7428N	7443J	7493N	74ALS137M
74290N	7443N	74ALS00M	74ALS137N
74293N	7444J	74ALS00N	74ALS138M
74298N	7444N	74ALS02M	74ALS138N
7430N	7445N	74ALS02N	74ALS14M
74320-1004	7446N	74ALS03BM	74ALS14N
74320-3004	7447N	74ALS03BN	74ALS151M
74320-4004	7448N	74ALS04BM	74ALS151N
74320-5000	7451N	74ALS04BN	74ALS153M

# Multisim 14.0 Education Components

---

74ALS153N	74ALS241AN	74ALS374AWM	74AS169AM
74ALS157M	74ALS241AWM	74ALS37AM	74AS169AN
74ALS157N	74ALS244AN	74ALS37AN	74AS174N
74ALS158M	74ALS244AWM	74ALS38AM	74AS181BN
74ALS158N	74ALS245AN	74ALS38AN	74AS181BNT
74ALS161BM	74ALS245AWM	74ALS74AM	74AS21M
74ALS161BN	74ALS251M	74ALS74AN	74AS21N
74ALS162BM	74ALS251N	74ALS86M	74AS240N
74ALS162BN	74ALS253M	74ALS86N	74AS240WM
74ALS163BM	74ALS253N	74AS00M	74AS244N
74ALS163BN	74ALS257M	74AS00N	74AS244WM
74ALS165M	74ALS257N	74AS04M	74AS245N
74ALS165N	74ALS258M	74AS04N	74AS245WM
74ALS169M	74ALS258N	74AS08M	74AS257M
74ALS169N	74ALS273N	74AS08N	74AS257N
74ALS174M	74ALS273WM	74AS10M	74AS258M
74ALS174N	74ALS27M	74AS10N	74AS258N
74ALS175M	74ALS27N	74AS157M	74AS27M
74ALS175N	74ALS30AM	74AS157N	74AS27N
74ALS20AM	74ALS30AN	74AS158M	74AS280M
74ALS20AN	74ALS32M	74AS158N	74AS280N
74ALS21AM	74ALS32N	74AS161M	74AS30M
74ALS21AN	74ALS373N	74AS161N	74AS30N
74ALS240AN	74ALS373WM	74AS163M	74AS32M
74ALS240AWM	74ALS374AN	74AS163N	74AS32N

# Multisim 14.0 Education Components

---

74AS34N	74F114D	74F157N	74F190N
74AS373N	74F114N	74F158AD	74F191D
74AS373WM	74F11D	74F158AN	74F191N
74AS374N	74F11N	74F158D	74F192D
74AS374WM	74F125D	74F158N	74F192N
74AS74M	74F125N	74F160AD	74F193D
74AS74N	74F126D	74F160AN	74F193N
74AS86M	74F126N	74F161AD	74F194D
74AS86N	74F138D	74F161AN	74F194N
74F00D	74F138N	74F162AD	74F195D
74F00N	74F139D	74F162AN	74F195N
74F02D	74F139N	74F163AD	74F20D
74F02N	74F13D	74F163AN	74F20N
74F04D	74F13N	74F164D	74F21D
74F04N	74F148D	74F164N	74F21N
74F08D	74F148N	74F169D	74F240D
74F08N	74F14D	74F169N	74F240N
74F109D	74F14N	74F174D	74F241D
74F109N	74F151D	74F174N	74F241N
74F10D	74F151N	74F175D	74F242D
74F10N	74F153D	74F175N	74F242N
74F112D	74F153N	74F181N	74F243D
74F112N	74F157AD	74F182D	74F243N
74F113D	74F157AN	74F182N	74F244D
74F113N	74F157D	74F190D	74F244N

# Multisim 14.0 Education Components

---

74F245D	74F350N	74F399D	74F640SC
74F245N	74F352D	74F399N	74F645PC
74F251D	74F352N	74F40D	74F645SC
74F251N	74F353D	74F40N	74F74D
74F253D	74F353N	74F51D	74F74N
74F253N	74F365D	74F51N	74F821PC
74F257D	74F365N	74F521DW	74F821SPC
74F257N	74F366D	74F521N	74F823PC
74F258AD	74F366N	74F533PC	74F823SPC
74F258AN	74F367D	74F533SC	74F825PC
74F258D	74F367N	74F534PC	74F825SPC
74F258N	74F368D	74F534SC	74F827PC
74F259D	74F368N	74F540PC	74F827SPC
74F259N	74F373D	74F540SC	74F828PC
74F273PC	74F373N	74F541PC	74F828SPC
74F273SC	74F374D	74F541SC	74F85D
74F27M	74F374N	74F563PC	74F85N
74F27N	74F378D	74F563SC	74F86D
74F280D	74F378N	74F564PC	74F86N
74F280N	74F379D	74F564SC	74HC00D_2V
74F283D	74F379N	74F573PC	74HC00D_4V
74F283N	74F37D	74F573SC	74HC00D_6V
74F32D	74F37N	74F574PC	74HC00N_2V
74F32N	74F38D	74F574SC	74HC00N_4V
74F350D	74F38N	74F640PC	74HC00N_6V



# Multisim 14.0 Education Components

---

74HC01D_2V	74HC05D_4V	74HC109D_6V	74HC114N_2V
74HC01D_4V	74HC05D_6V	74HC109N_2V	74HC114N_4V
74HC01D_6V	74HC05N_2V	74HC109N_4V	74HC114N_6V
74HC01N_2V	74HC05N_4V	74HC109N_6V	74HC11D_2V
74HC01N_4V	74HC05N_6V	74HC10D_2V	74HC11D_4V
74HC01N_6V	74HC08D_2V	74HC10D_4V	74HC11D_6V
74HC02D_2V	74HC08D_4V	74HC10D_6V	74HC11N_2V
74HC02D_4V	74HC08D_6V	74HC10N_2V	74HC11N_4V
74HC02D_6V	74HC08N_2V	74HC10N_4V	74HC11N_6V
74HC02N_2V	74HC08N_4V	74HC10N_6V	74HC125N_2V
74HC02N_4V	74HC08N_6V	74HC112D_2V	74HC125N_4V
74HC02N_6V	74HC09D_2V	74HC112D_4V	74HC125N_6V
74HC03D_2V	74HC09D_4V	74HC112D_6V	74HC126N_2V
74HC03D_4V	74HC09D_6V	74HC112N_2V	74HC126N_4V
74HC03D_6V	74HC09N_2V	74HC112N_4V	74HC126N_6V
74HC03N_2V	74HC09N_4V	74HC112N_6V	74HC133D_2V
74HC03N_4V	74HC09N_6V	74HC113D_2V	74HC133D_4V
74HC03N_6V	74HC107D_2V	74HC113D_4V	74HC133D_4V
74HC04D_2V	74HC107D_4V	74HC113D_6V	74HC133D_6V
74HC04D_4V	74HC107D_6V	74HC113N_2V	74HC133N_2V
74HC04D_6V	74HC107N_2V	74HC113N_4V	74HC133N_4V
74HC04N_2V	74HC107N_4V	74HC113N_6V	74HC133N_6V
74HC04N_4V	74HC107N_6V	74HC114D_2V	74HC137D_2V
74HC04N_6V	74HC109D_2V	74HC114D_4V	74HC137D_4V
74HC05D_2V	74HC109D_4V	74HC114D_6V	74HC137D_6V

# Multisim 14.0 Education Components

---

74HC137N_2V	74HC148N_6V	74HC153N_2V	74HC160N_4V
74HC137N_4V	74HC14D_2V	74HC153N_4V	74HC160N_6V
74HC137N_6V	74HC14D_4V	74HC153N_6V	74HC161D_2V
74HC138D_2V	74HC14D_6V	74HC154DW_2V	74HC161D_4V
74HC138D_4V	74HC14N_2V	74HC154DW_4V	74HC161D_6V
74HC138D_4V	74HC14N_4V	74HC154DW_6V	74HC161N_2V
74HC138D_6V	74HC14N_6V	74HC154NT_2V	74HC161N_4V
74HC138N_2V	74HC151D_2V	74HC154NT_4V	74HC161N_6V
74HC138N_4V	74HC151D_4V	74HC154NT_6V	74HC162D_2V
74HC138N_4V	74HC151D_6V	74HC157D_2V	74HC162D_4V
74HC138N_6V	74HC151N_2V	74HC157D_4V	74HC162D_6V
74HC139DW_2V	74HC151N_4V	74HC157D_6V	74HC162N_2V
74HC139DW_4V	74HC151N_6V	74HC157N_2V	74HC162N_4V
74HC139DW_6V	74HC152D_2V	74HC157N_4V	74HC162N_6V
74HC139N_2V	74HC152D_4V	74HC157N_6V	74HC163D_2V
74HC139N_4V	74HC152D_6V	74HC158D_2V	74HC163D_4V
74HC139N_6V	74HC152N_2V	74HC158D_4V	74HC163D_6V
74HC147N_2V	74HC152N_4V	74HC158D_6V	74HC163N_2V
74HC147N_4V	74HC152N_6V	74HC158N_2V	74HC163N_4V
74HC147N_6V	74HC153D_2V	74HC158N_4V	74HC163N_6V
74HC148DW_2V	74HC153D_4V	74HC158N_6V	74HC164N_2V
74HC148DW_4V	74HC153D_6V	74HC160D_2V	74HC164N_4V
74HC148DW_6V	74HC153DW_2V	74HC160D_4V	74HC164N_6V
74HC148N_2V	74HC153DW_4V	74HC160D_6V	74HC165D_2V
74HC148N_4V	74HC153DW_6V	74HC160N_2V	74HC165D_4V

# Multisim 14.0 Education Components

---

74HC165D_6V	74HC175N_2V	74HC192N_4V	74HC21N_6V
74HC165N_2V	74HC175N_4V	74HC192N_6V	74HC240DW_2V
74HC165N_4V	74HC175N_6V	74HC193D_2V	74HC240DW_4V
74HC165N_6V	74HC180D_2V	74HC193D_4V	74HC240DW_6V
74HC166D_2V	74HC180D_4V	74HC193D_6V	74HC240N_2V
74HC166D_4V	74HC180D_6V	74HC193N_2V	74HC240N_4V
74HC166D_6V	74HC180N_2V	74HC193N_4V	74HC240N_6V
74HC166N_2V	74HC180N_4V	74HC193N_6V	74HC241DW_2V
74HC166N_4V	74HC180N_6V	74HC194N_2V	74HC241DW_4V
74HC166N_6V	74HC190D_2V	74HC194N_4V	74HC241DW_6V
74HC173D_2V	74HC190D_4V	74HC194N_6V	74HC241N_2V
74HC173D_4V	74HC190D_6V	74HC195N_2V	74HC241N_4V
74HC173D_6V	74HC190N_2V	74HC195N_4V	74HC241N_6V
74HC173N_2V	74HC190N_4V	74HC195N_6V	74HC242N_2V
74HC173N_4V	74HC190N_6V	74HC20D_2V	74HC242N_4V
74HC173N_6V	74HC191D_2V	74HC20D_4V	74HC242N_6V
74HC174D_2V	74HC191D_4V	74HC20D_6V	74HC243N_2V
74HC174D_4V	74HC191D_6V	74HC20N_2V	74HC243N_4V
74HC174D_6V	74HC191N_2V	74HC20N_4V	74HC243N_6V
74HC174N_2V	74HC191N_4V	74HC20N_6V	74HC244_4V
74HC174N_4V	74HC191N_6V	74HC21D_2V	74HC244DW_2V
74HC174N_6V	74HC192D_2V	74HC21D_4V	74HC244DW_4V
74HC175D_2V	74HC192D_4V	74HC21D_6V	74HC244DW_6V
74HC175D_4V	74HC192D_6V	74HC21N_2V	74HC244N_2V
74HC175D_6V	74HC192N_2V	74HC21N_4V	74HC244N_4V

# Multisim 14.0 Education Components

---

74HC244N_6V	74HC258D_2V	74HC27D_4V	74HC30N_6V
74HC245DW_2V	74HC258D_4V	74HC27D_6V	74HC32D_2V
74HC245DW_4V	74HC258D_6V	74HC27N_2V	74HC32D_4V
74HC245DW_6V	74HC258N_2V	74HC27N_4V	74HC32D_6V
74HC245N_2V	74HC258N_4V	74HC27N_6V	74HC32N_2V
74HC245N_4V	74HC258N_6V	74HC280D_2V	74HC32N_4V
74HC245N_6V	74HC259D_2V	74HC280D_4V	74HC32N_6V
74HC251D_2V	74HC259D_4V	74HC280D_6V	74HC365D_2V
74HC251D_4V	74HC259D_6V	74HC280N_2V	74HC365D_4V
74HC251D_6V	74HC259N_2V	74HC280N_4V	74HC365D_6V
74HC251N_2V	74HC259N_4V	74HC280N_6V	74HC365N_2V
74HC251N_4V	74HC259N_6V	74HC283D_2V	74HC365N_4V
74HC251N_6V	74HC266D_2V	74HC283D_4V	74HC365N_6V
74HC253D_2V	74HC266D_4V	74HC283D_6V	74HC366D_2V
74HC253D_4V	74HC266D_6V	74HC283N_2V	74HC366D_4V
74HC253D_6V	74HC266N_2V	74HC283N_4V	74HC366D_6V
74HC253N_2V	74HC266N_4V	74HC283N_6V	74HC366N_2V
74HC253N_4V	74HC266N_6V	74HC298N_2V	74HC366N_4V
74HC253N_6V	74HC273DW_2V	74HC298N_4V	74HC366N_6V
74HC257D_2V	74HC273DW_4V	74HC298N_6V	74HC367D_2V
74HC257D_4V	74HC273DW_6V	74HC30D_2V	74HC367D_4V
74HC257D_6V	74HC273N_2V	74HC30D_4V	74HC367D_6V
74HC257N_2V	74HC273N_4V	74HC30D_6V	74HC367N_2V
74HC257N_4V	74HC273N_6V	74HC30N_2V	74HC367N_4V
74HC257N_6V	74HC27D_2V	74HC30N_4V	74HC367N_6V

# Multisim 14.0 Education Components

---

74HC368D_2V	74HC375D_4V	74HC379N_6V	74HC51N_2V
74HC368D_4V	74HC375D_6V	74HC386D_2V	74HC51N_4V
74HC368D_6V	74HC375N_2V	74HC386D_4V	74HC51N_6V
74HC368N_2V	74HC375N_4V	74HC386D_6V	74HC73D_2V
74HC368N_4V	74HC375N_6V	74HC386N_2V	74HC73D_4V
74HC368N_6V	74HC377DW_2V	74HC386N_4V	74HC73D_6V
74HC36D_2V	74HC377DW_4V	74HC386N_6V	74HC73N_2V
74HC36D_4V	74HC377DW_6V	74HC390D_2V	74HC73N_4V
74HC36D_6V	74HC377N_2V	74HC390D_4V	74HC73N_6V
74HC36N_2V	74HC377N_4V	74HC390D_6V	74HC74D_2V
74HC36N_4V	74HC377N_6V	74HC390N_2V	74HC74D_4V
74HC36N_6V	74HC378D_2V	74HC390N_4V	74HC74D_6V
74HC373DW_2V	74HC378D_4V	74HC390N_6V	74HC74N_2V
74HC373DW_4V	74HC378D_6V	74HC393N_2V	74HC74N_4V
74HC373DW_6V	74HC378N_2V	74HC393N_4V	74HC74N_6V
74HC373N_2V	74HC378N_4V	74HC393N_6V	74HC75D_2V
74HC373N_4V	74HC378N_6V	74HC42D_2V	74HC75D_4V
74HC373N_6V	74HC379D_2V	74HC42D_4V	74HC75D_6V
74HC374DW_2V	74HC379D_4V	74HC42D_6V	74HC75N_2V
74HC374DW_4V	74HC379D_6V	74HC42N_2V	74HC75N_4V
74HC374DW_6V	74HC379J_2V	74HC42N_4V	74HC75N_6V
74HC374N_2V	74HC379J_4V	74HC42N_6V	74HC76D_2V
74HC374N_4V	74HC379J_6V	74HC51D_2V	74HC76D_4V
74HC374N_6V	74HC379N_2V	74HC51D_4V	74HC76D_6V
74HC375D_2V	74HC379N_4V	74HC51D_6V	74HC76N_2V

# Multisim 14.0 Education Components

---

74HC76N_4V	74HC86N_6V	74LS08J	74LS113D
74HC76N_6V	74LS00D	74LS08J	74LS113N
74HC77D_2V	74LS00D	74LS08N	74LS113N
74HC77D_4V	74LS00N	74LS08N	74LS114D
74HC77D_6V	74LS00N	74LS09D	74LS114D
74HC77N_2V	74LS01D	74LS09D	74LS114N
74HC77N_4V	74LS01N	74LS09N	74LS114N
74HC77N_6V	74LS02D	74LS09N	74LS11D
74HC78D_2V	74LS02D	74LS107D	74LS11D
74HC78D_4V	74LS02N	74LS107D	74LS11N
74HC78D_6V	74LS02N	74LS107N	74LS11N
74HC78N_2V	74LS03D	74LS107N	74LS125D
74HC78N_4V	74LS03D	74LS109D	74LS125D
74HC78N_6V	74LS03N	74LS109D	74LS125N
74HC85AD_2V	74LS03N	74LS109N	74LS126D
74HC85AD_4V	74LS04D	74LS109N	74LS126D
74HC85AD_6V	74LS04D	74LS10D	74LS126N
74HC85AN_2V	74LS04N	74LS10D	74LS12D
74HC85AN_4V	74LS04N	74LS10N	74LS12D
74HC85AN_6V	74LS05D	74LS10N	74LS12N
74HC86D_2V	74LS05D	74LS112D	74LS12N
74HC86D_4V	74LS05N	74LS112D	74LS132D
74HC86D_6V	74LS05N	74LS112N	74LS132D
74HC86N_2V	74LS08D	74LS112N	74LS132N
74HC86N_4V	74LS08D	74LS113D	74LS132N

# Multisim 14.0 Education Components

---

74LS136D	74LS148N	74LS157N	74LS164D
74LS136N	74LS14D	74LS157N	74LS164N
74LS137D	74LS14D	74LS158D	74LS164N
74LS137N	74LS14N	74LS158D	74LS165D
74LS138D	74LS14N	74LS158N	74LS165D
74LS138D	74LS151D	74LS158N	74LS165N
74LS138N	74LS151D	74LS15D	74LS165N
74LS138N	74LS151N	74LS15D	74LS166D
74LS139D	74LS151N	74LS15N	74LS166D
74LS139D	74LS152J	74LS15N	74LS166N
74LS139N	74LS152N	74LS160D	74LS166N
74LS139N	74LS153D	74LS160D	74LS169D
74LS13D	74LS153D	74LS160N	74LS169D
74LS13N	74LS153N	74LS160N	74LS169N
74LS145D	74LS153N	74LS161D	74LS169N
74LS145D	74LS155D	74LS161N	74LS173D
74LS145N	74LS155D	74LS162D	74LS173D
74LS145N	74LS155N	74LS162D	74LS173N
74LS147D	74LS155N	74LS162N	74LS173N
74LS147D	74LS156D	74LS162N	74LS174D
74LS147N	74LS156D	74LS163D	74LS174D
74LS147N	74LS156N	74LS163D	74LS174N
74LS148D	74LS156N	74LS163N	74LS174N
74LS148D	74LS157D	74LS163N	74LS175D
74LS148N	74LS157D	74LS164D	74LS175D

# Multisim 14.0 Education Components

---

74LS175N	74LS194N	74LS241N	74LS253N
74LS175N	74LS195D	74LS241N	74LS257D
74LS181DW	74LS195D	74LS242D	74LS257D
74LS181DW	74LS195N	74LS242N	74LS257N
74LS181N	74LS195N	74LS243D	74LS257N
74LS181N	74LS19AD	74LS243N	74LS258D
74LS183D	74LS19AN	74LS244DW	74LS258D
74LS183N	74LS20D	74LS244N	74LS258N
74LS190D	74LS20D	74LS245DW	74LS258N
74LS190D	74LS20N	74LS245N	74LS259D
74LS190N	74LS20N	74LS247D	74LS259N
74LS190N	74LS21D	74LS247N	74LS266D
74LS191D	74LS21D	74LS248D	74LS266D
74LS191D	74LS21N	74LS248N	74LS266N
74LS191N	74LS21N	74LS249J	74LS266N
74LS191N	74LS22D	74LS249N	74LS26D
74LS192D	74LS22D	74LS24AD	74LS26D
74LS192D	74LS22N	74LS24AN	74LS26N
74LS192N	74LS22N	74LS251D	74LS26N
74LS192N	74LS240DW	74LS251D	74LS273DW
74LS193D	74LS240DW	74LS251N	74LS273DW
74LS193N	74LS240N	74LS251N	74LS273N
74LS194D	74LS240N	74LS253D	74LS273N
74LS194D	74LS241DW	74LS253D	74LS279D
74LS194N	74LS241DW	74LS253N	74LS279N



# Multisim 14.0 Education Components

---

74LS27D	74LS298N	74LS365D	74LS377DW
74LS27D	74LS30D	74LS365D	74LS377N
74LS27N	74LS30N	74LS365N	74LS377N
74LS27N	74LS30N	74LS365N	74LS378D
74LS280D	74LS32D	74LS366D	74LS378D
74LS280D	74LS32D	74LS366N	74LS378N
74LS280N	74LS32N	74LS367D	74LS378N
74LS280N	74LS32N	74LS367D	74LS379D
74LS283D	74LS33D	74LS367N	74LS379D
74LS283N	74LS33D	74LS367N	74LS379N
74LS28D	74LS33N	74LS368D	74LS379N
74LS28D	74LS33N	74LS368D	74LS37D
74LS28N	74LS348D	74LS368N	74LS37D
74LS28N	74LS348N	74LS368N	74LS37N
74LS290D	74LS352D	74LS373DW	74LS386D
74LS290D	74LS352D	74LS373DW	74LS386N
74LS290N	74LS352N	74LS373N	74LS38D
74LS290N	74LS352N	74LS373N	74LS38D
74LS293D	74LS353D	74LS374DW	74LS38N
74LS293D	74LS353D	74LS374DW	74LS38N
74LS293N	74LS353N	74LS374N	74LS390D
74LS293N	74LS363D	74LS374N	74LS390N
74LS298D	74LS363N	74LS375D	74LS393D
74LS298D	74LS364D	74LS375N	74LS393D
74LS298N	74LS364N	74LS377DW	74LS393N

# Multisim 14.0 Education Components

---

74LS393N	74LS466N	74LS54D	74LS75N
74LS395D	74LS466N	74LS54N	74LS75N
74LS395D	74LS467DW	74LS54N	74LS76D
74LS395N	74LS467N	74LS55D	74LS76D
74LS395N	74LS468DW	74LS55D	74LS76N
74LS399D	74LS468N	74LS55N	74LS76N
74LS399N	74LS47D	74LS55N	74LS77W
74LS40D	74LS47D	74LS640DW	74LS77W
74LS40D	74LS47N	74LS640N	74LS78D
74LS40N	74LS47N	74LS645DW	74LS78D
74LS40N	74LS48D	74LS645N	74LS78N
74LS42D	74LS48D	74LS69D	74LS78N
74LS42D	74LS48N	74LS69D	74LS83D
74LS42N	74LS48N	74LS69N	74LS83N
74LS42N	74LS49D	74LS69N	74LS85D
74LS445D	74LS49N	74LS73D	74LS85N
74LS445D	74LS51D	74LS73D	74LS86D
74LS445N	74LS51D	74LS73N	74LS86D
74LS445N	74LS51N	74LS73N	74LS86N
74LS465DW	74LS51N	74LS74D	74LS86N
74LS465DW	74LS540DW	74LS74D	74LS90D
74LS465N	74LS540N	74LS74N	74LS90D
74LS465N	74LS541DW	74LS74N	74LS90N
74LS466DW	74LS541N	74LS75D	74LS90N
74LS466DW	74LS54D	74LS75D	74LS91D

# Multisim 14.0 Education Components

---

74LS91D	74S09N	74S151N	74S195D
74LS91N	74S10D	74S153D	74S195N
74LS91N	74S10N	74S153N	74S20D
74LS92D	74S112D	74S157D	74S20N
74LS92D	74S112N	74S157N	74S22D
74LS92N	74S113D	74S158D	74S22N
74LS92N	74S113N	74S158N	74S240DW
74LS93D	74S114D	74S15D	74S240N
74LS93D	74S114N	74S15N	74S241DW
74LS93N	74S11D	74S162D	74S241N
74LS93N	74S11N	74S162N	74S244DW
74S00D	74S132D	74S163D	74S244N
74S00N	74S132N	74S163N	74S251D
74S02D	74S133D	74S169D	74S251N
74S02N	74S133N	74S169N	74S253D
74S03D	74S134D	74S174D	74S253N
74S03N	74S134D	74S174N	74S257D
74S04D	74S134N	74S175D	74S257N
74S04N	74S135D	74S175N	74S258D
74S05D	74S135N	74S181DW	74S258N
74S05N	74S138D	74S181N	74S280D
74S08D	74S138N	74S182D	74S280N
74S08J	74S139D	74S182N	74S283D
74S08N	74S139N	74S194D	74S283N
74S09D	74S151D	74S194N	74S30D

# Multisim 14.0 Education Components

---

74S30N	74STD116N	75 pF [C1206C750KBGAC TU]	750 pF [C0603C751K5GACT U]
74S32D	74STD150N		
74S32N	74STD154N	75 pF [C1210C750KBGAC TU]	750 pF [C0603C751K5HACT U]
74S350D	74STD159N		
74S350N	74STD16N	75 pF [C1812C750KBGAC TU]	750 pF [C1210C751KBGAC TU]
74S373DW	74STD17N		
74S373N	74STD198N	75 pF [C1825C750KBGAC TU]	750 pF [C1812C751KBGAC TU]
74S374DW	74STD199N		
74S374N	74STD25N	75 pF [C2220C750KBGAC TU]	750 pF [C1825C751KBGAC TU]
74S37D	74STD39N		
74S37N	74STD45N	75 pF [C2225C750KBGAC TU]	750 pF [C2220C751KBGAC TU]
74S38D	74STD72N		
74S38N	75 mF [C0805C759KBGAC TU]	750 pF [C0402C751K1HACT U]	750 pF [C2225C751KBGAC TU]
74S40D			
74S40N	75 pF [C0603C750K5GACT U]	750 pF [C0402C751K3HACT U]	750 pF [C2225C751KBGAC TU]
74S51D			
74S51N	75 pF [C0805C750K2GACT U]	750 pF [C0402C751K5HACT U]	75LQ150 75SLQ030
74S74D			
74S74N	75 pF [C0805C750KBGAC TU]	750 pF [C0603C751K1HACT U]	75SLQ045 75SLQ060
74S85D			
74S85N	75 pF [C0805C750KCGAC TU]	750 pF [C0603C751K3HACT U]	777778-01 777779-01
74S86D			
74S86N	75 pF [C1206C750K5GACT U]		779157-01 781334-01
74STD06N			
74STD07N			7Line_Bussed

# Multisim 14.0 Education Components

---

7Line_Isolated	8.2 nF [C0805C822K1GACT U]	8.2 nF [C1206C822K1HACT U]	8.2 nF [C1812C822K5RACT U]
7POS_ROTARY	8.2 nF [C0805C822K1HACT U]	8.2 nF [C1206C822K1RACT U]	8.2 nF [C2220C822K2GACT U]
8.2 nF [C0402C822K3RACT U]	8.2 nF [C0805C822K1HACT U]	8.2 nF [C1206C822K1RACT U]	8.2 nF [C2220C822K2GACT U]
8.2 nF [C0402C822K4RACT U]	8.2 nF [C0805C822K1RACT U]	8.2 nF [C1206C822K2RACT U]	8.2 uF [A700V825M016AT E045]
8.2 nF [C0402C822K5RACT U]	8.2 nF [C0805C822K2RACT U]	8.2 nF [C1206C822K3HACT U]	8.2 uF [C1206C825K4PACT U]
8.2 nF [C0402C822K9RACT U]	8.2 nF [C0805C822K3GACT U]	8.2 nF [C1206C822K5HACT U]	8.2 uF [C1206C825K8PACT U]
8.2 nF [C0603C822K1RACT U]	8.2 nF [C0805C822K3HACT U]	8.2 nF [C1206C822K5RACT U]	8.2 uF [C1206C825K8RACT U]
8.2 nF [C0603C822K3GACT U]	8.2 nF [C0805C822K3RACT U]	8.2 nF [C1206C822KARACT U]	8.2 uF [C1206C825K9RACT U]
8.2 nF [C0603C822K3HACT U]	8.2 nF [C0805C822K4RACT U]	8.2 nF [C1210C822K5GACT U]	8.2 uF [C1210C825K3PACT U]
8.2 nF [C0603C822K3RACT U]	8.2 nF [C0805C822K5GACT U]	8.2 nF [C1210C822K5RACT U]	8.2 uF [C1210C825K4PACT U]
8.2 nF [C0603C822K4RACT U]	8.2 nF [C0805C822K5HACT U]	8.2 nF [C1210C822KARACT U]	80CLQ150
8.2 nF [C0603C822K5RACT U]	8.2 nF [C0805C822K5RACT U]	8.2 nF [C1812C822K5GACT U]	80SCLQ030
			80SCLQ060
			80SQ045NG
			80SQ045NRLG

# Multisim 14.0 Education Components

---

82 mF [C0603C829K2GACT U]	82 nF [C0805C823K3RACT U]	82 nF [C1206C823K3RACT U]	82 nF [C1210C823K1RACT U]
82 mF [C0805C829K5GACT U]	82 nF [C0805C823K4RACT U]	82 nF [C1206C823K5HACT U]	82 nF [C1210C823K3HACT U]
82 mF [C0805C829KBGAC TU]	82 nF [C0805C823K5RACT U]	82 nF [C1206C823K5RACT U]	82 nF [C1210C823K5GACT U]
82 nF [C0402C823K4RACT U]	82 nF [C0805C823K8RACT U]	82 nF [C1206C823KARACT U]	82 nF [C1210C823K5HACT U]
82 nF [C0402C823K8RACT U]	82 nF [C0805C823M5UAC TU]	82 nF [C1206C823M5UAC TU]	82 nF [C1210C823K5RACT U]
82 nF [C0402C823K9RACT U]	82 nF [C0805F823K3RACT U]	82 nF [C1206F823K1RACT U]	82 nF [C1210C823KARACT U]
82 nF [C0603C823K3RACT U]	82 nF [C0805F823K4RACT U]	82 nF [C1206F823K3RACT U]	82 nF [C1210C823M1UAC TU]
82 nF [C0603C823K4RACT U]	82 nF [C0805F823K5RACT U]	82 nF [C1206F823K4RACT U]	82 nF [C1210F823K2RACT U]
82 nF [C0603C823K5RACT U]	82 nF [C1206C823K1RACT U]	82 nF [C1206F823K5RACT U]	82 nF [C1812C823K1GACT U]
82 nF [C0603C823K8RACT U]	82 nF [C1206C823K2RACT U]	82 nF [C1210C823K1GACT U]	82 nF [C1812C823K1HACT U]
82 nF [C0805C823K1RACT U]	82 nF [C1206C823K3HACT U]	82 nF [C1210C823K1HACT U]	82 nF [C1812C823K5GACT U]

# Multisim 14.0 Education Components

---

82 nF [C1812C823K5HACT U]	82 pF [C0805C820K3GACT U]	82 pF [C2220C820KBGAC TU]	82 uF [A700V826M2R5AT E025]
82 nF [C1812C823K5RACT U]	82 pF [C0805C820K5GACT U]	82 pF [C2225C820KBGAC TU]	82 uF [A700V826M2R5AT E028]
82 nF [C2220C823K1GACT U]	82 pF [C0805C820KBGAC TU]	82 pF [CA064C820K2GAC TU]	82 uF [T520C826M008AT E025]
82 nF [C2220C823K2GACT U]	82 pF [C1206C820K1GACT U]	82 pF [CDR31BP820BKSM ]	82 uF [T520C826M008AT E045]
82 nF [C2220C823K5GACT U]	82 pF [C1206C820K2GACT U]	82 uF [A700V826M004AT E018]	820 nF [C0603C824K8PACT U]
82 pF [C0201C820K3GACT U]	82 pF [C1206C820K5GACT U]	82 uF [A700V826M004AT E025]	820 nF [C0805C824K4RACT U]
82 pF [C0402C820K3GACT U]	82 pF [C1206C820KBGAC TU]	82 uF [A700V826M004AT E028]	820 nF [C0805C824K8RACT U]
82 pF [C0402C820K5GACT U]	82 pF [C1206C820KCGAC TU]	82 uF [A700V826M006AT E018]	820 nF [C1206C824K3RACT U]
82 pF [C0603C820K5GACT U]	82 pF [C1210C820KBGAC TU]	82 uF [A700V826M006AT E025]	820 nF [C1206C824K4RACT U]
82 pF [C0805C820K1GACT U]	82 pF [C1812C820KBGAC TU]	82 uF [A700V826M006AT E028]	820 nF [C1206F824K4RACT U]
82 pF [C0805C820K2GACT U]	82 pF [C1825C820KBGAC TU]	82 uF [A700V826M2R5AT E018]	820 nF [C1210C824K5RACT U]

# Multisim 14.0 Education Components

---

820 nF [C1210C824K8RACT U]	820 nF [C2220C824KARACT U]	820 pF [C0603C821K1HACT U]	820 pF [C0805C821K2RACT U]
820 nF [C1210F824K3RACT U]	820 nF [C2225C824K5RACT U]	820 pF [C0603C821K1RACT U]	820 pF [C0805C821K4GACT U]
820 nF [C1210F824K4RACT U]	820 nF [C2225C824KARACT U]	820 pF [C0603C821K2RACT U]	820 pF [C0805C821K4RACT U]
820 nF [C1812C824K5RACT U]	820 pF [C0402C821K1HACT U]	820 pF [C0603C821K3GACT U]	820 pF [C0805C821K5GACT U]
820 nF [C1812C824M5UAC TU]	820 pF [C0402C821K3GACT U]	820 pF [C0603C821K3HACT U]	820 pF [C0805C821K5RACT U]
820 nF [C1812F824K1RACT U]	820 pF [C0402C821K3HACT U]	820 pF [C0603C821K3RACT U]	820 pF [C1206C821K1GACT U]
820 nF [C1812F824K3RACT U]	820 pF [C0402C821K3RACT U]	820 pF [C0603C821K4RACT U]	820 pF [C1206C821K2GACT U]
820 nF [C1812F824K5RACT U]	820 pF [C0402C821K4RACT U]	820 pF [C0603C821K5GACT U]	820 pF [C1206C821K5GACT U]
820 nF [C1825C824KARACT U]	820 pF [C0402C821K5HACT U]	820 pF [C0603C821K5HACT U]	820 pF [C1210C821KBGAC TU]
820 nF [C2220C824K1RACT U]	820 pF [C0402C821K5RACT U]	820 pF [C0603C821K5RACT U]	820 pF [C1812C821K2GACT U]
820 nF [C2220C824K5RACT U]	820 pF [C0402C821K8RACT U]	820 pF [C0805C821K1RACT U]	820 pF [C1812C821K5GACT U]



# Multisim 14.0 Education Components

---

820 pF [C1812C821KBGAC TU]	9.1 nF [C0805C912K1HACT U]	91 pF [C0805C910KBGAC TU]	910 pF [C0603C911K1HACT U]
820 pF [C1825C821KBGAC TU]	9.1 nF [C0805C912K3HACT U]	91 pF [C1206C910K1GACT U]	910 pF [C0603C911K3HACT U]
820 pF [C2220C821KBGAC TU]	9.1 nF [C0805C912K5GACT U]	91 pF [C1206C910KBGAC TU]	910 pF [C0603C911K5GACT U]
820 pF [C2225C821KBGAC TU]	9.1 nF [C0805C912K5HACT U]	91 pF [C1210C910KBGAC TU]	910 pF [C0603C911K5HACT U]
820 pF [CDR32BP821BKSM ]	9.1 nF [C1206C912K1HACT U]	91 pF [C1812C910KBGAC TU]	910 pF [C0805C911K5GACT U]
8550-4500PL  87520-0010BLF	9.1 nF [C1206C912K3GACT U]	91 pF [C1825C910KBGAC TU]	910 pF [C1210C911KBGAC TU]
8EQ045  8EWS08S	9.1 nF [C1206C912K3HACT U]	91 pF [C2220C910KBGAC TU]	910 pF [C1812C911KBGAC TU]
8EWS10S  8EWS12S	9.1 nF [C1206C912K5HACT U]	91 pF [C2225C910KBGAC TU]	910 pF [C1825C911KBGAC TU]
8Line_Bussed  8Line_Isolated	9.1 nF [CDR35BP912BKSM ]	910 pF [C0402C911K1HACT U]	910 pF [C2220C911KBGAC TU]
8POS_ROTARY			
9.1 nF [C0603C912K3HACT U]	90CLQ100  91 mF [C0805C919KBGAC TU]	910 pF [C0402C911K3HACT U]	910 pF [C2225C911KBGAC TU]
9.1 nF [C0805C912K1GACT U]	91 pF [C0805C910K2GACT U]	910 pF [C0402C911K5HACT U]	9Line_Bussed  9Line_Isolated  A+jB_BLOCK

# Multisim 14.0 Education Components

---

ABC_TO_DQ	ACB1608M-080	ACML-7420-000E	ACPL-217-560E
ABM_CURRENT	ACB1608M-120	ACNW261L-000E	ACPL-217-56AE
ABM_VOLTAGE	ACB1608M-300	ACNW261L-300E	ACPL-217-56BE
AC_CURRENT	ACB1608M-600	ACPL-021L-000E	ACPL-217-56CE
AC_POWER	ACB2012H-015	ACPL-021L-060E	ACPL-217-56DE
AC_VOLTAGE	ACB2012H-030	ACPL-024L-000E	ACPL-312U-000E
ACA3216H4-060	ACB2012H-060	ACPL-024L-060E	ACPL-312U-300E
ACA3216H4-120	ACB2012H-120	ACPL-054L-000E	ACPL-32JT-000E
ACA3216H4-300	ACB2012H-300	ACPL-054L-060E	ACPL-331J-000E
ACA3216M3-600	ACB2012L-015	ACPL-061L-000E	ACPL-332J-000E
ACA3216M4-060	ACB2012L-030	ACPL-061L-060E	ACPL-336J-000E
ACA3216M4-120	ACB2012L-060	ACPL-064L-000E	ACPL-337J-000E
ACA3216M4-300	ACB2012L-120	ACPL-064L-060E	ACPL-339J-000E
ACA3216M4-600	ACB2012L-300	ACPL-077L-000E	ACPL-34JT-000E
ACB1608H-015	ACB2012L-600	ACPL-077L-060E	ACPL-782T-000E
ACB1608H-030	ACB2012M-040	ACPL-0820-000E	ACPL-782T-300E
ACB1608H-060	ACB2012M-080	ACPL-214-500E	ACPL-C61L-000E
ACB1608H-120	ACB2012M-120	ACPL-214-50AE	ACPL-C61L-060E
ACB1608H-300	ACB2012M-300	ACPL-214-560E	ACPL-C790-000E
ACB1608L-015	ACB2012M-600	ACPL-214-56AE	ACPL-C79A-000E
ACB1608L-030	ACC2012L-250	ACPL-217-500E	ACPL-C79B-000E
ACB1608L-060	ACC3216L-500	ACPL-217-50AE	ACPL-C87AT-000E
ACB1608L-120	ACC4516L-700	ACPL-217-50BE	ACPL-H342-000E
ACB1608L-300	ACML-7400-000E	ACPL-217-50CE	ACPL-H342-060E
ACB1608M-040	ACML-7410-000E	ACPL-217-50DE	ACPL-K342-000E

# Multisim 14.0 Education Components

---

ACPL-K342-060E	ACPL-M71T-000E	ACPL-W50L-060E	AD509JH
ACPL-K34T-000E	ACPL-M71T-060E	ACPL-W61L-000E	AD509KH
ACPL-K34T-060E	ACPL-M72T-000E	ACPL-W61L-060E	AD509SH
ACPL-K43T-000E	ACPL-M72T-060E	ACSL-6400-00TE	AD515AJH
ACPL-K43T-060E	ACPL-P340-000E	ACSL-6400-06TE	AD515AKH
ACPL-K44T-000E	ACPL-P340-060E	ACSL-7210-00RE	AD515ALH
ACPL-K44T-060E	ACPL-P341-000E	ACSL-7210-06RE	AD517JH
ACPL-K54L-000E	ACPL-P341-060E	ACTEL-FLASHPRO-HDR	AD517KH
ACPL-K54L-060E	ACPL-P343-000E	AD1580ART	AD517LH
ACPL-K64L-000E	ACPL-P343-060E	AD1580ARTZ	AD517SH
ACPL-K64L-060E	ACPL-P345-000E	AD1580BKSZ	AD536AJD
ACPL-M21L-000E	ACPL-P345-060E	AD1580BRT	AD536AJH
ACPL-M21L-060E	ACPL-P346-000E	AD1580BRTZ	AD536AJQ
ACPL-M43T-000E	ACPL-P346-060E	AD22050N	AD536ASE/883B
ACPL-M43T-060E	ACPL-W340-000E	AD22050R	AD542JH
ACPL-M46T-000E	ACPL-W340-060E	AD22057N	AD542KH
ACPL-M46T-060E	ACPL-W341-000E	AD22057R	AD542LH
ACPL-M49T-000E	ACPL-W341-060E	AD380JH	AD542SH
ACPL-M49T-060E	ACPL-W343-000E	AD380KH	AD544JH
ACPL-M50L-000E	ACPL-W343-060E	AD380LH	AD544KH
ACPL-M50L-060E	ACPL-W345-000E	AD380SH	AD544LH
ACPL-M61L-000E	ACPL-W345-060E	AD507JH	AD544SH
ACPL-M61L-060E	ACPL-W346-000E	AD507KH	AD545AJH
ACPL-M61T-000E	ACPL-W346-060E	AD507SH	AD545AKH
ACPL-M61T-060E	ACPL-W50L-000E		AD545ALH

# Multisim 14.0 Education Components

---

AD545AMH	AD549SH	AD587JRZ	AD604ARS
AD546JN	AD549SH/883B	AD587KN	AD605AN
AD546KN	AD5530_SO16	AD587KR	AD605AR
AD547JH	AD5531_SO16	AD587KRZ	AD620AN
AD547KH	AD5539JN	AD587UQ	AD620AR
AD547LH	AD5539JQ	AD588AD	AD620BN
AD547SH	AD5539SQ	AD588AQ	AD620BR
AD548AH	AD5539SQ/883B	AD588ARWZ	AD620SQ
AD548AQ	AD581JH	AD588BD	AD623AN
AD548AR	AD581KH	AD588BQ	AD623AR
AD548BH	AD581LH	AD588JQ	AD623ARM
AD548BQ	AD581SH	AD588KQ	AD623BN
AD548BR	AD581TH	AD588SD	AD623BR
AD548CH	AD581UH	AD588TD	AD624AD
AD548CQ	AD584JH	AD588TQ/883B	AD624BD
AD548JN	AD584JN	AD600AQ	AD624CD
AD548JR	AD584KH	AD600AR	AD624SD
AD548KN	AD584KN	AD600JN	AD626AN
AD548SH	AD584LH	AD602AQ	AD626AR
AD548SQ	AD584SH	AD602AR	AD626BN
AD548TH	AD584TH	AD602JN	AD627AN
AD548TQ	AD587JN	AD603AQ	AD627AR
AD549JH	AD587JNZ	AD603AR	AD627BN
AD549KH	AD587JQ	AD604AN	AD627BR
AD549LH	AD587JR	AD604AR	AD628ARMZ

# Multisim 14.0 Education Components

---

AD628ARZ	AD637JD	AD647JH	AD705TQ
AD629AN	AD637JDZ	AD647KH	AD706AQ
AD629AR	AD637JQ	AD647LH	AD706AR
AD629BN	AD637JRZ	AD647SE	AD706BQ
AD629BR	AD637JRZ-R7	AD647SEB	AD706JN
AD630AD	AD637JRZ-RL	AD647SH	AD706JR
AD630AR	AD637KDZ	AD680AN	AD706KN
AD630BD	AD637KQ	AD680AR	AD706TQ
AD630JN	AD637KRZ	AD680JR	AD707AH
AD630KN	AD637SD	AD680JTZ	AD707AQ
AD630SD	AD637SD/883B	AD704AN	AD707AR
AD630SE/883B	AD637SQ/883B	AD704AQ	AD707JN
AD633AN	AD642JH	AD704AR	AD707KN
AD633AR	AD642KH	AD704BQ	AD707KR
AD633JN	AD642LH	AD704JN	AD707TH
AD633JR	AD642SH	AD704JR	AD707TQ
AD636JD	AD644JH	AD704JR-16	AD708AH
AD636JH	AD644KH	AD704KN	AD708AQ
AD636KD	AD644LH	AD704TQ	AD708BH
AD636KH	AD644SH	AD704TQ/883B	AD708BQ
AD637AQ	AD645AH	AD705AQ	AD708JN
AD637AR	AD645BH	AD705BQ	AD708SH
AD637ARZ	AD645JN	AD705JN	AD708SH/883B
AD637BR	AD645KN	AD705JR	AD708SQ
AD637BRZ	AD645SH	AD705KN	AD711AH

# Multisim 14.0 Education Components

---

AD711AQ	AD712SQ/883B	AD737BQ	AD744CH
AD711BH	AD712TH	AD741CH	AD744CQ
AD711BQ	AD712TQ	AD741CN	AD744JN
AD711CH	AD712TRZ-EP	AD741H	AD744JR
AD711CQ	AD713AQ	AD741JH	AD744KN
AD711JN	AD713BQ	AD741JN	AD744KR
AD711JR	AD713JN	AD741KH	AD744SH
AD711KN	AD713JR	AD741KN	AD744SQ
AD711KR	AD713JR-16	AD741LH	AD744TH
AD711SH	AD713KN	AD741LN	AD744TH/883B
AD711SQ	AD713SQ	AD741SH	AD744TQ
AD711TH	AD713SQ/883B	AD743AN	AD745AN
AD711TQ	AD713TQ	AD743AQ	AD745AQ
AD712AH	AD713TQ/883B	AD743AR	AD745AR
AD712AQ	AD734AN	AD743BQ	AD745BQ
AD712BH	AD734AQ	AD743JN	AD745JN
AD712BQ	AD734BN	AD743JR	AD745JR
AD712CH	AD734BQ	AD743KN	AD745KN
AD712CQ	AD734SQ	AD743KR	AD745SQ
AD712JN	AD734SQ/883B	AD743SQ	AD745SQ/883B
AD712JR	AD736AQ	AD743SQ/883B	AD746AQ
AD712KN	AD736AR	AD744AH	AD746BQ
AD712KR	AD736JNZ	AD744AQ	AD746JN
AD712SH	AD737AN	AD744BH	AD746JR
AD712SQ	AD737AR	AD744BQ	AD746SQ

# Multisim 14.0 Education Components

---

AD780AN	AD8002AR	AD8012ARMZ	AD8027ARTZ-REEL7
AD780AR	AD8002ARM	AD8014AR	AD8027ARZ
AD780BN	AD8003ACPZ	AD8014ART	AD8027ARZ-REEL
AD780BR	AD8003ACPZ-R2	AD8016ARB	AD8027ARZ-REEL7
AD795BH	AD8004AN	AD8016ARE	AD8028ARMZ
AD795JN	AD8004AR	AD8016AREZ	AD8028ARZ
AD795JR	AD8004AR-14	AD8016ARP	AD8029AKS
AD795JRZ	AD8004SQ	AD8017AR	AD8029AR
AD795KN	AD8005AN	AD8018AR	AD8030AR
AD796AN	AD8005AR	AD8018ARU	AD8030ARJ
AD796AR	AD8005ART	AD8021AR	AD8031AN
AD796BN	AD8007AKS	AD8021ARM	AD8031ANZ
AD796SQ/883B	AD8007AR	AD8021ARMZ	AD8031AR
AD797AN	AD8008AR	AD8021ARZ	AD8031ART
AD797AR	AD8008ARM	AD8022AR	AD8031ARTZ
AD797BN	AD8009AR	AD8022ARM	AD8031ARZ
AD797SQ	AD8009ARZ	AD8022ARMZ	AD8031BN
AD8000YCPZ	AD8009JRT	AD8022ARZ	AD8031BNZ
AD8000YCPZ-REEL	AD8010AN	AD8023AR	AD8031BR
AD8000YRDZ	AD8010AR	AD8024AR	AD8031BRZ
AD8001AN	AD8010AR-16	AD8027AR	AD8032AN
AD8001AQ	AD8011AN	AD8027ART	AD8032ANZ
AD8001AR	AD8011AR	AD8027ARTZ	AD8032AR
AD8001ART	AD8012AR	AD8027ARTZ-R2	AD8032ARM
AD8002AN	AD8012ARM	AD8027ARTZ-REEL	AD8032ARMZ

# Multisim 14.0 Education Components

---

AD8032ARZ	AD8045ARD	AD8062AR	AD8099ARDZ
AD8032BN	AD8045ARDZ	AD8062ARM	AD810AN
AD8032BNZ	AD8047AN	AD8062ARMZ	AD810AR
AD8032BR	AD8047AR	AD8062ARZ	AD810SN
AD8032BRZ	AD8048AN	AD8065AR	AD810SR
AD8033AKS	AD8048AR	AD8065ART	AD811AN
AD8033AR	AD8051AR	AD8065ARTZ	AD811AR-16
AD8034AR	AD8051ART	AD8065ARZ	AD811AR-20
AD8034ART	AD8052AR	AD8066AR	AD811JR
AD8036AN	AD8052ARM	AD8066ARM	AD811SE/883B
AD8036AR	AD8054AR	AD8066ARMZ	AD811SQ/883B
AD8038AKS	AD8054ARU	AD8066ARZ	AD8129ARMZ
AD8038AR	AD8055AN	AD8067ART	AD8129ARMZ-REEL
AD8039AR	AD8055AR	AD8072ARM	AD8129ARMZ-REEL7
AD8039ART	AD8055ART	AD8072JN	AD8129ARZ
AD8040AR	AD8055ARZ	AD8072JR	AD8129ARZ-REEL
AD8040ARU	AD8056AN	AD8079AR	AD8129ARZ-REEL7
AD8041AN	AD8056AR	AD8079BR	AD812AN
AD8041AR	AD8056ARM	AD8091AR	AD812AR
AD8042AN	AD8057AR	AD8091ART	AD8130AR
AD8042AR	AD8057ART	AD8092AR	AD8130ARM
AD8044AN	AD8058AR	AD8092ARM	AD8131AR
AD8044AR	AD8058ARM	AD8099ACP	AD8131ARM
AD8045ACP	AD8061AR	AD8099ACPZ-R2	AD8131ARMZ
AD8045ACPZ-R2	AD8061ART	AD8099ARD	



# Multisim 14.0 Education Components

---

AD8131ARZ	AD8148ACPZ-R2	AD8208WBRZ	AD8220ARMZ-R7
AD8132AR	AD815ARB-24	AD8209WBRMZ	AD8220ARMZ-RL
AD8132ARM	AD817AN	AD820AN	AD8220BRMZ
AD8132ARMZ	AD817AR	AD820AR	AD8220BRMZ-R7
AD8132ARZ	AD8184AN	AD820BN	AD8220BRMZ-RL
AD8133ACP-R2	AD818AN	AD820BR	AD8220WARMZ
AD8137YCP	AD818AR	AD8210WYRZ	AD8220WARMZ-R7
AD8137YCPZ	AD8205WHRZ	AD8210YRZ	AD8220WARMZ-RL
AD8137YR	AD8205WHRZ-RL	AD8211YRJZ-R2	AD8221AR
AD8137YRZ	AD8205WYRZ	AD8214ARMZ	AD8221ARM
AD8138AR	AD8205WYRZ-R7	AD8216WYRZ	AD8221BR
AD8138ARM	AD8205WYRZ-RL	AD8216WYRZ-R7	AD8222ACPZ-R7
AD8138ARMZ	AD8205YRZ	AD8216WYRZ-RL	AD8222BCPZ-R7
AD8138ARZ	AD8205YRZ-R7	AD8216YRZ	AD8222HACPZ-R7
AD8139ACP	AD8205YRZ-RL	AD8216YRZ-R7	AD8222HBCPZ-R7
AD8139ACPZ	AD8206WYRZ	AD8216YRZ-RL	AD8224ACPZ-R7
AD8139ACPZ-R2	AD8206WYRZ-R7	AD8217BRMZ	AD8224ACPZ-RL
AD8139ARD	AD8206WYRZ-RL	AD8217BRMZ-R7	AD8224ACPZ-WP
AD8139ARDZ	AD8206YRZ	AD8217BRMZ-RL	AD8224BCPZ-R7
AD813AN	AD8206YRZ-REEL	AD8218BCPZ-RL	AD8224BCPZ-RL
AD813AR	AD8206YRZ-REEL7	AD8218BRMZ	AD8224BCPZ-WP
AD813AR-14	AD8207WBRZ	AD8218BRMZ-R7	AD8224HACPZ-R7
AD8145YCPZ-R2	AD8207WBRZ-R7	AD8219BRMZ	AD8224HACPZ-RL
AD8146ACPZ-R2	AD8207WBRZ-RL	AD8219BRMZ-RL	AD8224HACPZ-WP
AD8147ACPZ-R2	AD8208WBRMZ	AD8220ARMZ	AD8224HBCPZ-R7

# Multisim 14.0 Education Components

---

AD8224HBCPZ-RL	AD8237ARMZ-R7	AD8274ARMZ-RL	AD828AR
AD8224HBCPZ-WP	AD8237ARMZ-RL	AD8274ARZ	AD829AQ
AD8225AR	AD823AN	AD8274ARZ-R7	AD829JN
AD8226ARMZ	AD823AR	AD8274ARZ-RL	AD829JR
AD8226ARZ	AD8244ARMZ	AD8275ARMZ	AD829SE/883B
AD8226BRMZ	AD8244BRMZ	AD8275BRMZ	AD829SQ
AD8226BRZ	AD824AN	AD8276ARMZ	AD829SQ/883B
AD8227ARMZ	AD824AR-14	AD8276ARZ	AD8304ARU
AD8227ARZ	AD824AR-16	AD8276BRMZ	AD830AN
AD8227BRMZ	AD824BN	AD8276BRZ	AD830JR
AD8227BRZ	AD8250ARMZ	AD8277ARZ	AD8310ARM
AD8228ARMZ	AD8251ARMZ	AD8277BRZ	AD8330ACPZ-R2
AD8228ARZ	AD8253ARMZ	AD8278ARMZ	AD8330ACPZ-R7
AD8228BRMZ	AD8253ARMZ-R7	AD8278ARZ	AD8330ACPZ-RL
AD8228BRZ	AD8253ARMZ-RL	AD8278BRMZ	AD8330ARQZ
AD8229HDZ	AD825AR	AD8278BRZ	AD8330ARQZ-R7
AD822AN	AD825AR-16	AD8279ARZ	AD8330ARQZ-RL
AD822AR	AD826AN	AD8279BRZ	AD8331ARQZ
AD822ARM	AD826AR	AD827AQ	AD8331ARQZ-R7
AD822BN	AD8270ACPZ-R7	AD827JN	AD8331ARQZ-RL
AD822BR	AD8273ARZ	AD827JR-16	AD8332ACPZ-R2
AD822SQ	AD8273ARZ-R7	AD827SE/883B	AD8332ACPZ-R7
AD8235ACBZ-P7	AD8273ARZ-RL	AD827SQ	AD8332ACPZ-RL
AD8236ARMZ	AD8274ARMZ	AD827SQ/883B	AD8332ARU
AD8237ARMZ	AD8274ARMZ-R7	AD828AN	AD8332ARU-REEL

# Multisim 14.0 Education Components

---

AD8332ARU-REEL7	AD840JQ	AD841SE	AD8422ARZ-R7
AD8332ARUZ	AD840KN	AD841SH	AD8422ARZ-RL
AD8332ARUZ-R7	AD840KQ	AD841SQ	AD8422BRMZ
AD8332ARUZ-RL	AD840SE-883B	AD8420ARMZ	AD8422BRMZ-R7
AD8333ACPZ-REEL	AD840SQ	AD8420ARMZ-R7	AD8422BRMZ-RL
AD8333ACPZ-REEL7	AD840SQ-883B	AD8420ARMZ-RL	AD8422BRZ
AD8333ACPZ-WP	AD8417BRMZ	AD8421ARMZ	AD8422BRZ-R7
AD8334ACPZ	AD8417WBRMZ	AD8421ARMZ-R7	AD8422BRZ-RL
AD8334ACPZ-REEL	AD8417WBRZ	AD8421ARMZ-RL	AD8426ACPZ-R7
AD8334ACPZ-REEL7	AD8417WHRMZ	AD8421ARZ	AD8426ACPZ-WP
AD8335ACPZ	AD8417WHRZ	AD8421ARZ-R7	AD8426BCPZ-R7
AD8335ACPZ-REEL	AD8418ABRMZ	AD8421ARZ-RL	AD8426BCPZ-WP
AD8335ACPZ-REEL7	AD8418AWBRMZ	AD8421BRMZ	AD8429ARZ
AD8336ACPZ-R7	AD8418AWBRZ	AD8421BRMZ-R7	AD8429ARZ-R7
AD8336ACPZ-RL	AD8418AWHRMZ	AD8421BRMZ-RL	AD8429BRZ
AD8336ACPZ-WP	AD8418AWHRZ	AD8421BRZ	AD8429BRZ-R7
AD8337BCPZ-R2	AD8418BRMZ	AD8421BRZ-R7	AD842JH
AD8337BCPZ-REEL	AD8418WBRMZ	AD8421BRZ-RL	AD842JN
AD8337BCPZ-REEL7	AD8418WBRZ	AD8421TRMZ-EP	AD842JQ
AD8337BCPZ-WP	AD841JH	AD8421TRMZ-EP-R7	AD842JR
AD8338ACPZ-R7	AD841JN	AD8422ARMZ	AD842KH
AD8338ACPZ-RL	AD841JQ	AD8422ARMZ-R7	AD842KN
AD8397ARDZ	AD841KH	AD8422ARMZ-RL	AD842KQ
AD8397ARZ	AD841KN	AD8422ARZ	AD842SE
AD840JN	AD841KQ		AD842SH

# Multisim 14.0 Education Components

---

AD842SQ	AD844AN	AD8475BRMZ	AD848AQ
AD8436ACPZ-R7	AD844AQ	AD8475BRMZ-R7	AD848JN
AD8436ACPZ-RL	AD844BQ	AD8475BRMZ-RL	AD848JR
AD8436ACPZ-WP	AD844JRZ-16	AD8476ACPZ-R7	AD848SQ
AD8436ARQZ	AD844SQ	AD8476ACPZ-RL	AD848SQ/883B
AD8436ARQZ-R7	AD8450ASTZ	AD8476ACPZ-WP	AD8494ARMZ
AD8436ARQZ-RL	AD8451ASTZ	AD8476ARMZ	AD8494ARMZ-R7
AD8436BRQZ	AD845AQ	AD8476ARMZ-R7	AD8494CRMZ
AD8436BRQZ-R7	AD845BQ	AD8476ARMZ-RL	AD8494CRMZ-R7
AD8436BRQZ-RL	AD845JN	AD8476BCPZ-R7	AD8495ARMZ
AD8436JCPZ-R7	AD845JR	AD8476BCPZ-RL	AD8495ARMZ-R7
AD8436JCPZ-RL	AD845JR-16	AD8476BCPZ-WP	AD8495CRMZ
AD8436JCPZ-WP	AD845KN	AD8476BRMZ	AD8495CRMZ-R7
AD843AQ	AD845SQ	AD8476BRMZ-R7	AD8496ARMZ
AD843BH	AD845SQ/883B	AD8476BRMZ-RL	AD8496ARMZ-R7
AD843BQ	AD846AN	AD8479ARZ	AD8496CRMZ
AD843JN	AD846AQ	AD8479ARZ-RL	AD8496CRMZ-R7
AD843JR	AD846BQ	AD8479BRZ	AD8497ARMZ
AD843JR-16	AD846SQ	AD8479BRZ-RL	AD8497ARMZ-R7
AD843KN	AD8475ACPZ-R7	AD847AQ	AD8497CRMZ
AD843SE	AD8475ACPZ-RL	AD847AR	AD8497CRMZ-R7
AD843SE/883B	AD8475ACPZ-WP	AD847JN	AD849AQ
AD843SH	AD8475ARMZ	AD847JR	AD849JN
AD843SQ	AD8475ARMZ-R7	AD847SQ	AD849JR
AD843SQ/883B	AD8475ARMZ-RL	AD847SQ/883B	AD849SQ

# Multisim 14.0 Education Components

---

AD849SQ/883B	AD8529ARM	AD8548ARZ-RL	AD8597ARZ
AD8500AKSZ	AD8531AKS	AD8551AR	AD8599ARZ
AD8502ARJZ	AD8531AR	AD8551ARM	AD8601ART
AD8504ARUZ	AD8532AR	AD8552AR	AD8602AR
AD8505ACBZ-R7	AD8532ARM	AD8552ARU	AD8602ARM
AD8505ARJZ-RL	AD8532ARU	AD8554AR	AD8603AUJZ
AD8506ARMZ	AD8534AR	AD8554ARU	AD8604AR
AD8508ACBZ-REEL	AD8534ARU	AD8561AN	AD8604ARQZ
AD8508ARUZ	AD8538ARZ	AD8561AR	AD8604ARUZ
AD8510AR	AD8538AUJZ	AD8561ARU	AD8604DRU
AD8510ARM	AD8538AUJZ-R2	AD8564AN	AD8604DRZ
AD8510BR	AD8539ARMZ	AD8564AR	AD8605ACB
AD8512AR	AD8539ARZ	AD8565AKS	AD8605ART
AD8512ARM	AD8541AKS	AD8565AKSZ	AD8606ACBZ-REEL
AD8512BR	AD8541AR	AD8571AR	AD8606AR
AD8513AR	AD8541ART	AD8571ARM	AD8606ARM-REEL
AD8513ARU	AD8541ARZ	AD8572AR	AD8607AR
AD8515AKS	AD8542AR	AD8572ARU	AD8607ARM-REEL
AD8515ART	AD8542ARM	AD8574AR	AD8608AR
AD8517ART	AD8542ARU	AD8574ARU	AD8608ARU
AD8519AKS	AD8544AR	AD8591ART	AD8609AR
AD8519AR	AD8544ARU	AD8592ARM	AD8609ARU
AD8519ART	AD8546ARMZ	AD8594AR	AD8610AR
AD8527AR	AD8548ARZ	AD8594ARU	AD8610ARM
AD8529AR	AD8548ARZ-R7	AD8597ACPZ-R2	AD8610ARZ

# Multisim 14.0 Education Components

---

AD8610BR	AD8624ARUZ	AD8638ARZ	AD8656ARMZ
AD8611AR	AD8625ARUZ	AD8639ACPZ-R2	AD8656ARZ
AD8611ARM	AD8625ARZ	AD8639ARMZ	AD8657ACPZ-RL
AD8612ARU	AD8626ARMZ	AD8639ARZ	AD8657ARMZ
AD8613AKSZ	AD8626ARZ	AD8639WARZ	AD8659ACPZ-R7
AD8613AUJZ	AD8627AKS	AD8641AKSZ	AD8659ACPZ-RL
AD8614ART	AD8627AKSZ	AD8641AKSZ-R2	AD8659ARZ
AD8615AUJZ	AD8627AR	AD8641ARZ	AD8659ARZ-R7
AD8616AR	AD8627ARZ	AD8642ARMZ	AD8659ARZ-RL
AD8616ARM	AD8628AR	AD8642ARZ	AD8661ACPZ-R2
AD8617ACPZ-R2	AD8628ART	AD8643ACPZ-R2	AD8661ARZ
AD8617ARMZ	AD8628AUJ	AD8643ARZ	AD8662ARMZ
AD8617ARZ	AD8629ARMZ	AD8644AR	AD8662ARZ
AD8617WARMZ-REEL	AD8629ARZ	AD8644ARU	AD8663ACPZ
	AD8629WARZ-RL	AD8646ARMZ	AD8663ARZ
AD8617WARZ-RL	AD8630ARUZ	AD8646ARZ	AD8664ARUZ
	AD8630ARZ	AD8646WARMZ-RL	AD8664ARZ
AD8618ARU	AD8630WARZ-RL	AD8646WARZ-RL	AD8667ARMZ
AD8619ARUZ	AD8631ART	AD8648ARUZ	AD8667ARZ
AD8619ARZ	AD8631ARTZ	AD8648ARZ	AD8669ARUZ
AD8620AR	AD8632AR	AD8648WARUZ	AD8669ARZ
AD8620BR	AD8632ARM	AD8651AR	AD8671AR
AD8622ARMZ	AD8632ARMZ	AD8651ARM	AD8671ARM
AD8622ARZ	AD8632ARZ	AD8655ARMZ	AD8671ARMZ
AD8624ACPZ-R2	AD8638ARJZ	AD8655ARZ	AD8672AR

# Multisim 14.0 Education Components

---

AD8672ARM	AD9617JN	ADA4000-1AUJZ-RL	ADA4004-4ARZ-R7
AD8672ARMZ	AD9617JR	ADA4000-2ARMZ	ADA4004-4ARZ-RL
AD8674AR	AD9617SQ	ADA4000-2ARZ	ADA4051-1AKSZ-R2
AD8674ARU	AD9617TQ	ADA4000-4ARUZ	ADA4051-1ARJZ-R2
AD8675ARMZ	AD9618AQ	ADA4000-4ARZ	ADA4051-2ACPZ-R2
AD8675ARZ	AD9618BQ	ADA4001-2ARZ	ADA4051-2ARMZ
AD8676ARMZ	AD9618JN	ADA4001-2ARZ-R7	ADA4062-2ACPZ-RL
AD8676ARZ	AD9618JR	ADA4001-2ARZ-RL	ADA4062-2ARMZ
AD8676BRMZ	AD9618SQ	ADA4004-1ARJZ-R2	ADA4062-2ARZ
AD8676BRZ	AD9618TQ	ADA4004-1ARJZ-R7	ADA4062-2BRZ
AD8677ARZ	AD9620AD	ADA4004-1ARJZ-RL	ADA4062-4ACPZ-R2
AD8677AUJZ-R2	AD9620SD	ADA4004-1ARZ	ADA4062-4ARUZ
AD8691AKSZ	AD9621AN	ADA4004-1ARZ-R7	ADA4075-2ACPZ-RL
AD8691AUJZ	AD9622AN	ADA4004-1ARZ-RL	ADA4075-2ARZ
AD8692ARMZ	AD9623AN	ADA4004-2ARMZ	ADA4077-1ARMZ
AD8692ARZ	AD9624AN	ADA4004-2ARMZ-R7	ADA4077-1ARZ
AD8694ARUZ	AD9630AN	ADA4004-2ARMZ-RL	ADA4077-1BRZ
AD8694ARZ	AD9630AQ	ADA4004-2ARZ	ADA4077-2ARMZ
AD8698AR	AD9630AR	ADA4004-2ARZ-R7	ADA4077-2ARMZ-RL
AD8698ARM	AD9631AN	ADA4004-2ARZ-RL	ADA4077-2ARMZ-R7
AD9218_FP48	AD9631AR	ADA4004-4ACPZ-R2	ADA4077-2ARZ
AD9610TH	AD9632AN	ADA4004-4ACPZ-R7	ADA4077-2ARZ-RL
AD9610TH/883B	AD9632AR	ADA4004-4ACPZ-RL	ADA4077-2BRZ
AD9617AQ	ADA4000-1ARZ	ADA4004-4ARZ	
AD9617BQ	ADA4000-1AUJZ		

# Multisim 14.0 Education Components

---

ADA4077-2BRZ-R7	ADA4500-2ACPZ-RL	ADA4627-1ACPZ-RL	ADA4666-2ARMZ-RL
ADA4077-2BRZ-RL	ADA4500-2ARMZ	ADA4627-1ARZ	ADA4691-2ACBZ-R7
ADA4077-4ARUZ	ADA4500-2ARMZ-R7	ADA4627-1BRZ	ADA4691-2ACPZ-R7
ADA4077-4ARZ	ADA4500-2ARMZ-RL	ADA4637-1ACPZ-R2	ADA4691-4ACPZ-R7
ADA4084-2ARMZ	ADA4505-1ACBZ-R7	ADA4637-1ARZ	ADA4692-2ACPZ-R7
ADA4084-2ARMZ-R7	ADA4505-1ARJZ-R2	ADA4637-1BRZ	ADA4692-2ARZ
ADA4084-2ARMZ-RL	ADA4505-2ACBZ-RL	ADA4638-1ACPZ-R7	ADA4692-4ARUZ
ADA4084-2ARZ	ADA4505-2ARMZ	ADA4638-1ACPZ-RL	ADA4700-1ARDZ
ADA4084-2ARZ-R7	ADA4505-4ACBZ-RL	ADA4638-1ARZ	ADA4805-1AKSZ-R2
ADA4084-2ARZ-RL	ADA4505-4ARUZ	ADA4638-1ARZ-R7	ADA4805-1ARJZ-R2
ADA4091-2ACPZ-R2	ADA4528-1ARMZ	ADA4638-1ARZ-RL	ADA4817-1ACPZ-R2
ADA4091-2ARZ	ADA4610-2ACPZ-R7	ADA4661-2ACPZ-R7	ADA4817-1ACPZ-R7
ADA4091-4ACPZ-R2	ADA4610-2ACPZ-RL	ADA4661-2ACPZ-RL	ADA4817-1ACPZ-RL
ADA4091-4ARUZ	ADA4610-2ARMZ	ADA4661-2ARMZ	ADA4817-1ARDZ
ADA4092-4ARUZ	ADA4610-2ARMZ-R7	ADA4661-2ARMZ-R7	ADA4817-1ARDZ-R7
ADA4096-2ACPZ-R7	ADA4610-2ARMZ-RL	ADA4661-2ARMZ-RL	ADA4817-1ARDZ-RL
ADA4096-2ARMZ	ADA4610-2ARZ	ADA4665-2ARMZ	ADA4817-2ACPZ-R2
ADA4096-2WARMZ-R7	ADA4610-2ARZ-R7	ADA4665-2ARZ	ADA4817-2ACPZ-R7
ADA4096-2WARMZ-RL	ADA4610-2ARZ-RL	ADA4666-2ACPZ-R7	ADA4817-2ACPZ-RL
ADA4096-4ACPZ-R7	ADA4610-2BRZ	ADA4666-2ACPZ-RL	ADA4841-1YRZ
ADA4096-4ARUZ	ADA4610-2BRZ-R7	ADA4666-2ARMZ	ADA4850-1YCPZ
ADA4500-2ACPZ-R7	ADA4610-2BRZ-RL	ADA4666-2ARMZ-R7	ADA4850-1YCPZ-R2
			ADA4850-2YCPZ-R2
			ADA4850-2YCPZ-RL



# Multisim 14.0 Education Components

---

ADA4851-1WYRJZ-R7	ADA4861-3YRZ	ADA4897-1ARZ	ADA4940-1ACPZ-R7
ADA4851-1YRJZ-R2	ADA4861-3YRZ-RL	ADA4897-1SRJZ-EPR7	ADA4940-1ACPZ-RL
ADA4851-1YRJZ-RL	ADA4861-3YRZ-RL7	ADA4897-2ARMZ	ADA4940-2ACPZ-R2
ADA4851-2WYRMZ	ADA4870ARRZ	ADA4897-2TRMZ-EP	ADA4940-2ACPZ-R7
ADA4851-2YRMZ	ADA4891-1ARJZ-R7	ADA4898-1YRDZ	ADA4940-2ACPZ-RL
ADA4851-2YRMZ-RL	ADA4891-1ARZ	ADA4898-2YRDZ	ADA4941-1YCPZ-RL
ADA4851-4WYRUZ	ADA4891-2ARMZ	ADA4899-1YCPZ	ADA4941-1YRZ
ADA4851-4YRUZ	ADA4891-2ARZ	ADA4899-1YCPZ-R2	ADA4950-1YCPZ-R2
ADA4851-4YRUZ-RL	ADA4891-3ARUZ	ADA4899-1YRDZ	ADA4950-2YCPZ-R2
ADA4853-1AKSZ-R2	ADA4891-3ARZ	ADA4922-1ACPZ-R2	ADA4960-1ACPZ-R2
ADA4853-2YCPZ-R2	ADA4891-4ARUZ	ADA4922-1ARDZ	ADC
ADA4853-3WYCPZ-R7	ADA4891-4ARZ	ADA4927-1YCPZ-R2	ADC16
ADA4853-3YCPZ-R2	ADA4895-2ARMZ	ADA4927-2YCPZ	ADD_FULL
ADA4853-3YRUZ	ADA4895-2ARMZ-R7	ADA4930-1YCPZ-R2	ADD_FULL4_FCR
ADA4855-3YCPZ-R2	ADA4895-2ARMZ-RL	ADA4930-2YCPZ-R2	ADD_HALF
ADA4857-1YCPZ-R2	ADA4896-2ACPZ-R2	ADA4932-1YCPZ-R2	ADG1211YCPZ-500RL7
ADA4857-1YRZ	ADA4896-2ACPZ-R7	ADA4932-2YCPZ-R2	ADG1211YRUZ
ADA4857-2YCPZ-R2	ADA4896-2ACPZ-RL	ADA4937-1YCPZ-R2	ADG1212YCPZ-500RL7
ADA4858-3ACPZ-R2	ADA4896-2ARMZ	ADA4937-2YCPZ-R2	ADG1212YRUZ
ADA4860-1YRJZ-R2	ADA4896-2ARMZ-R7	ADA4938-1ACPZ-R2	ADG1213YCPZ-500RL7
ADA4860-1YRJZ-RL	ADA4896-2ARMZ-RL	ADA4938-2ACPZ-R2	ADG1213YRUZ
ADA4860-1YRJZ-RL7	ADA4897-1ARJZ-R2	ADA4939-1YCPZ-R2	ADG1236YCPZ-500RL7
		ADA4939-2YCPZ-R2	
		ADA4940-1ACPZ-R2	

# Multisim 14.0 Education Components

---

ADG1236YRUZ	ADG411BRZ	ADG444ABR	ADG513BR
ADG1311YRUZ	ADG411TQ	ADG444BN	ADG513PM5
ADG1311YRZ	ADG412	ADG444BR	ADG513TQ
ADG1312YRUZ	ADG412BN	ADG444S	ADG528F
ADG1312YRZ	ADG412BR	ADG508FBN	ADG528FBN
ADG1313YRUZ	ADG412BRU	ADG508FBNZ	ADG528FBP
ADG1313YRZ	ADG412BRUZ	ADG508FBRN	ADG528FTQ
ADG406BN	ADG412BRZ	ADG508FBRUZ	ADG601BRMZ
ADG406BP	ADG412TQ	ADG508FBRW	ADG601BRTZ-REEL
ADG407BN	ADG413BN	ADG508FTQ	ADG602BRM
ADG407BP	ADG413BNZ	ADG509FBN	ADG602BRTZ-REEL
ADG408	ADG413BR	ADG509FBRN	ADG604YRU
ADG408BN	ADG413BRUZ	ADG509FBRUZ	ADG604YRUZ
ADG408BR	ADG413BRZ	ADG509FBRW	ADG608BN
ADG408BRU	ADG426BN	ADG509FBRWZ	ADG608BR
ADG408TQ	ADG426BRS	ADG509FTQ	ADG608BRU
ADG409BN	ADG441ABN	ADG511BN	ADG608TRU
ADG409BR	ADG441ABR	ADG511BR	ADG609BN
ADG409BRU	ADG441BN	ADG511PM5	ADG609BR
ADG409TQ	ADG441BR	ADG511TQ	ADG609BRU
ADG411	ADG441TQ	ADG512BN	ADG609BRUZ
ADG411BN	ADG442BN	ADG512BR	ADG609BRZ
ADG411BR	ADG442SQ	ADG512PM5	ADG611YRUZ
ADG411BRU	ADG444	ADG512TQ	ADG611YRZ
ADG411BRUZ	ADG444ABN	ADG513BN	

# Multisim 14.0 Education Components

---

ADG612WYRUZ-REEL	ADG721ACPZ-REEL	ADG811YCPZ-REEL	ADR3425ARJZ-R7
ADG612YRUZ	ADG721BRM	ADG811YRU	ADR5040AKSZ-R2
ADG613YRUZ	ADG722ACPZ-REEL	ADG812YRU	ADR5040ARTZ-R2
ADG658YCPZ	ADG722BRM	ADG813YRU	ADR5040BKSZ-R2
ADG658YRQ	ADG723ACPZ-REEL	ADG819BCB	ADR5040BRTZ-R2
ADG658YRU	ADG723BRM	ADG819BRM	ADS8320EB
ADG659YCPZ	ADG741BKSZ5-REEL	ADG819BRT	ADS8322YB
ADG659YRQ	ADG741BKSZ-REEL	ADG820BRM	ADS8364Y
ADG659YRU	ADG742BKSZ5-REEL	ADG820BRT	ADTL082ARMZ
ADG663BRU	ADG742BKSZ-R2	ADG821BRM	ADTL082ARZ
ADG701BRJ-500RL7	ADG749BKSZ-REEL	ADG822BRM	ADTL082JR
ADG701BRM	ADG779BKSZ-R2	ADG823BRM	ADTL082JRZ
ADG701BRTZ-REEL	ADG781BCP	ADG839YKSZ-500RL7	ADTL084ARUZ
ADG702BRJ-REEL7	ADG782BCP	ADG841YKSZ-500RL7	ADTL084ARZ
ADG702BRM	ADG783BCP	ADG842YKSZ-500RL7	ADTL084JR
ADG702BRTZ-REEL	ADG787BCBZ-REEL	ADG849YKSZ-500RL7	ADTL084JRZ
ADG711BR	ADG787BCPZ-REEL	ADG859BRYZ-REEL	ADZS-BRKOUT-EX3
ADG711BRU	ADG787BRMZ	ADG859YRYZ-REEL	AIR_NC
ADG712BR	ADG801BRM	ADG884BCBZ-REEL	AIR_NO
ADG712BRU	ADG801BRT-500RL7	ADG884BCPZ-REEL	A-jB_BLOCK
ADG713BR	ADG802BCBZ-REEL7	ADG884BRMZ	ALPHA_NUMERIC_COM_A_BLUE
ADG713BRU	ADG802BRM	ADR3425ARJZ-R2	ALPHA_NUMERIC_COM_A_GREEN
ADG719BRM	ADG802BRT-500RL7		ALPHA_NUMERIC_COM_A_ORANGE

# Multisim 14.0 Education Components

---

ALPHA_NUMERIC_COM_A_RED	AMP01GS	AND5	ASSR-V621-302E
ALPHA_NUMERIC_COM_A_YELLOW	AMP02AZ	AND6	ASSR-V622-002E
ALPHA_NUMERIC_COM_K_BLUE	AMP02EP	AND6	ASSR-V622-302E
ALPHA_NUMERIC_COM_K_GREEN	AMP02ES	AND7	ATP207-TL-H
ALPHA_NUMERIC_COM_K_ORANGE	AMP02FP	AND7	ATP301-TL-H
ALPHA_NUMERIC_COM_K_RED	AMP02FS	AND8	ATP405-TL-H
ALPHA_NUMERIC_COM_K_YELLOW	AMP04EP	AND8	AUIRF2903ZL
ALTERA-BYTEBLASTER-HDR	AMP04ES	ANGLE_WRAP	AUIRF2903ZS
ALU_4BIT	AMP04FP	ANTI_PLUG	AUIRF3004WL
AM_VOLTAGE	AMP04FS	ARBITRARY_LAPLAC E_FUNCTION	AUIRF7303QTR
AM29705DC	AMPSIMP	ARBITRARY_LOAD	AUIRF7640S2TR
AM29705PC	ANALOG_AND	ARBITRARY_LOGIC_BLOCK_16_16	AUIRF7647S2TR
AMMETER_H	ANALOG_INV	ARBITRARY_LOGIC_BLOCK_4_4	AUIRF7648M2TR
AMMETER_HR	ANALOG_OR	ARBITRARY_LOGIC_BLOCK_8_8	AUIRF7669L2TR
AMMETER_V	ANALOG_SR_LATCH	ARBITRARY_SPICE_BLOCK	AUIRF7734M2TR
AMMETER_VR	AND_OR_I	ARM-14-HDR	AUIRF7736M2TR
AMP01AX	AND2	ARM-20-HDR	AUIRF7737L2TR
AMP01BX	AND2	ASP-134488-01	AUIRF7738L2TR
AMP01EX	AND3	ASP-134603-01	AUIRF7739L2TR
AMP01FX	AND3	ASP-134604-01	AUIRFR4292
	AND4	ASP-134606-01	AUIRFR4292TRL
	AND5	ASSR-V621-002E	AUIRFR4292TRR
			AUIRFS6535
			AUIRFS6535TRL
			AUIRFS8407

# Multisim 14.0 Education Components

---

AUIRFS8407TRL	AVR-JTAG-HDR	BA885	BAR_LED_YELLOW_TEN
AUIRFS8408	B6S-E3/80	BA892	BAR14-1
AUIRFS8408TRL	BA157GP	BA895	BAR15-1
AUIRFS8408TRR	BA158GP	BAL74	BAR16-1
AUIRFSL6535	BA159-E3/54	BAL99	BAR50-02L
AUIRFSL8408	BA159GP	BAR_LED_BLUE	BAR50-02V
AUIRFU4292	BA220	BAR_LED_BLUE_FOUR	BAR61
AUIRFZ44VZS	BA221	BAR_LED_BLUE_TEN	BAR63-02L
AUIRGDC0250	BA223	BAR_LED_GREEN	BAR63-02V
AUIRGP4063D	BA281	BAR_LED_GREEN_FOUR	BAR63-02W
AUIRGP4063D-E	BA314	BAR_LED_GREEN_TEN	BAR63-03W
AUIRGP4066D1	BA315	BAR_LED_ORANGE	BAR63-04
AUIRGP4066D1-E	BA316	BAR_LED_ORANGE_FOUR	BAR63-04W
AUIRGP50B60PD1	BA317	BAR_LED_ORANGE_TEN	BAR63-05
AUIRGP50B60PD1E	BA318	BAR_LED_ORANGE_FOUR	BAR63-05W
AUIRGPS4067D1	BA423	BAR_LED_ORANGE_TEN	BAR63-06
AUIRGR4045D	BA423L	BAR_LED_RED	BAR63-06W
AUIRGR4045DTR	BA481	BAR_LED_RED_FOUR	BAR64-02V
AUIRGR4045DTRL	BA482	BAR_LED_RED_TEN	BAR64-03W
AUIRGR4045DTRR	BA483	BAR_LED_YELLOW	BAR64-04
AUIRGU4045D	BA484	BAR_LED_YELLOW_FOUR	BAR64-04W
AUIRLS3034-7P	BA592	BAR_LED_YELLOW_TEN	BAR64-05W
AUIRLS3034-7TRL	BA595	BAR_LED_YELLOW_FOUR	BAR64-06W
AUIRLS3114Z	BA682		BAR65-03W
AUIRLS3114ZTRL	BA683		

# Multisim 14.0 Education Components

---

BAR67-02V	BAS16M3T5G	BAS29	BAS45
BAR74	BAS16P2T5G	BAS3010B-03W	BAS45A
BAR81W	BAS16T	BAS3020B	BAS45AL
BAR88-02V	BAS16VV	BAS31	BAS45L
BAR99	BAS16VY	BAS316	BAS516
BAS101	BAS16W	BAS32	BAS521
BAS101S	BAS17	BAS321	BAS56
BAS11	BAS170W	BAS32L	BAS70
BAS116	BAS19	BAS35	BAS70-02L
BAS116H	BAS20	BAS40	BAS70-02W
BAS116LT1G	BAS20LT1G	BAS40-02L	BAS70-04
BAS116T	BAS21	BAS40-04	BAS70-04LT1G
BAS116TT1G	BAS21AVD	BAS40-05	BAS70-04W
BAS125-04W	BAS21AW	BAS40-05V	BAS70-05
BAS125-05W	BAS21H	BAS40-05W	BAS70-05W
BAS125-07W	BAS21HT1G	BAS40-06	BAS70-06
BAS140W	BAS21J	BAS40-06W	BAS70-06W
BAS15	BAS21M3T5G	BAS40-07	BAS70-07
BAS16	BAS21SLT1G	BAS40-07V	BAS70-07S
BAS16-02L	BAS21SW	BAS40-07W	BAS70-07V
BAS16DXV6T1G	BAS21TMR6T1G	BAS40H	BAS70H
BAS16H	BAS21U	BAS40L	BAS70L
BAS16J	BAS21VD	BAS40W	BAS70VV
BAS16L	BAS21W	BAS40XY	BAS70W
BAS16LD	BAS28	BAS416	BAS70XY

# Multisim 14.0 Education Components

---

BAS716	BAT17-05	BAT54S	BAT66-05
BAS81	BAT17-05W	BAT54SW	BAT68
BAS82	BAT17-06W	BAT54T	BAT68-04
BAS83	BAT17-07	BAT54VV	BAT68-04W
BAS85	BAT18	BAT54W	BAT68-06
BAS86	BAT18-04	BAT54WT1G	BAT68-06W
BAT120A	BAT18-05	BAT54XY	BAT720
BAT120C	BAT24-02LS	BAT60A	BAT721
BAT120S	BAT240A	BAT60B	BAT721A
BAT14_098	BAT46WH	BAT62	BAT721C
BAT15_03W	BAT46WJ	BAT62-02L	BAT721S
BAT15_04	BAT54	BAT62-02W	BAT74
BAT15_098	BAT54A	BAT62-03W	BAT74S
BAT15_099	BAT54AW	BAT62-07W	BAT74V
BAT15_099R	BAT54C	BAT63	BAT754
BAT15-02LRH	BAT54CLT1	BAT63-07W	BAT754A
BAT15-03W	BAT54CLT1G	BAT64	BAT754C
BAT15-05W	BAT54CLT3G	BAT64-02W	BAT754L
BAT15-099	BAT54CM	BAT64-04	BAT754S
BAT160A	BAT54CV	BAT64-04W	BAT760
BAT160C	BAT54CW	BAT64-05	BAT81
BAT160S	BAT54H	BAT64-05W	BAT82
BAT165	BAT54J	BAT64-06	BAT83
BAT17	BAT54L	BAT64-06W	BAT85
BAT17-04	BAT54M3T5G	BAT65	BAT854AW

# Multisim 14.0 Education Components

---

BAT854CW	BAV70LT1	BAW56LT1G	BB405B
BAT854SW	BAV70LT1G	BAW56LT3G	BB417
BAT854W	BAV70LT3G	BAW56M	BB439
BAT86	BAV70M	BAW56M3T5G	BB515
BAT960	BAV70M3T5G	BAW56S	BB535
BAV10	BAV70S	BAW56T	BB545
BAV100	BAV70T	BAW56TT1G	BB555
BAV101	BAV70TT1G	BAW56W	BB555-02V
BAV102	BAV70W	BAW62	BB565
BAV103	BAV74	BAW78D	BB565-02V
BAV105	BAV74LT1	BAX12	BB619
BAV170	BAV74LT1G	BAX14	BB620
BAV18	BAV756S	BAX18	BB639
BAV19	BAV99	BAY80	BB639C
BAV199	BAV99LT1	BB112	BB640
BAV199W	BAV99LT1G	BB119	BB644
BAV20	BAV99LT3	BB130	BB659
BAV21	BAV99LT3G	BB204B	BB659C
BAV23	BAV99S	BB204G	BB659C-02V
BAV23A	BAV99W	BB212	BB664
BAV23C	BAW101	BB215	BB664-02V
BAV23S	BAW101S	BB219	BB689
BAV45	BAW156	BB240	BB689-02V
BAV70	BAW56	BB241	BB804
BAV70DXV6T5G	BAW56LT1	BB249	BB809



# Multisim 14.0 Education Components

---

BB811	BBY56-02W	BC238BP	BC52PA
BB814	BBY56-03W	BC239BP	BC53-10PA
BB833	BBY57-02V	BC264A	BC53-16PA
BB837	BBY57-02W	BC264B	BC53PA
BB857	BBY57-05W	BC264C	BC54-10PA
BB909A	BBY58-02V	BC264D	BC54-16PA
BB909B	BBY58-02W	BC307AP	BC546BP
BB910	BBY58-03W	BC308AP	BC547BG
BB911	BBY58-05W	BC327	BC547BP
BB914	BBY58-06W	BC328	BC547BRL1G
BBY31	BBY62	BC337	BC547BZL1G
BBY39	BBY65-02V	BC337AP	BC548BP
BBY40	BBY66-02V	BC338	BC549BP
BBY42	BBY66-05W	BC338AP	BC54PA
BBY51-02W	BC107BP	BC368	BC550BP
BBY51-03W	BC108BP	BC369	BC55-10PA
BBY52-02L	BC109BP	BC413BP	BC55-16PA
BBY52-02W	BC177AP	BC414BP	BC556AP
BBY53-02L	BC178AP	BC415AP	BC557AP
BBY53-02V	BC182BP	BC416AP	BC557BG
BBY53-02W	BC183BP	BC51-10PA	BC557BRL1G
BBY53-03W	BC184BP	BC51-16PA	BC557BZL1G
BBY53-05W	BC212AP	BC51PA	BC558AP
BBY55-02V	BC213AP	BC52-10PA	BC559AP
BBY55-03W	BC237BP	BC52-16PA	BC55PA

# Multisim 14.0 Education Components

---

BC560AP	BC807-40	BC818-16	BC847AM
BC56-10PA	BC807-40LT1G	BC818-25	BC847AMB
BC56-16PA	BC807-40LT3G	BC818-40	BC847AT
BC56PA	BC807-40QA	BC846	BC847AW
BC635	BC807-40W	BC846A	BC847B
BC636	BC807DS	BC846ALT1G	BC847BDW1T1G
BC637	BC807W	BC846ALT3G	BC847BDW1T3
BC638	BC808-16	BC846AT	BC847BDW1T3G
BC639	BC808-25	BC846AW	BC847BM
BC640	BC808-40	BC846B	BC847BMB
BC68-25PA	BC817	BC846BDW1T1G	BC847BPDW1T1
BC68PA	BC817-16	BC846BLT1G	BC847BPDW1T1G
BC69-16PA	BC817-16W	BC846BLT3G	BC847BPDW1T2G
BC69-25PA	BC817-25	BC846BMB	BC847BPDW1T3G
BC69PA	BC817-25LT1	BC846BPDW1T1G	BC847BPDV6T1G
BC807	BC817-25LT1G	BC846BPN	BC847BPN
BC807-16	BC817-25LT3G	BC846BS	BC847BS
BC807-16LT1G	BC817-25QA	BC846BT	BC847BT
BC807-16LT3G	BC817-25W	BC846BW	BC847BV
BC807-16W	BC817-40	BC846DS	BC847BVN
BC807-25	BC817-40QA	BC846S	BC847BW
BC807-25LT1G	BC817-40W	BC846T	BC847C
BC807-25LT3G	BC817DPN	BC846W	BC847CDV6T1G
BC807-25QA	BC817DS	BC847	BC847CM
BC807-25W	BC817W	BC847A	BC847CMB

# Multisim 14.0 Education Components

---

BC847CT	BC856B	BC857CM	BC868-25
BC847CTT1G	BC856BDW1T1G	BC857CMB	BC869
BC847CW	BC856BDW1T3G	BC857CT	BC869-16
BC847DS	BC856BS	BC857CW	BC869-25
BC847T	BC856BT	BC857T	BCD_7SEG_DCD
BC847W	BC856BW	BC857W	BCM61B
BC848	BC856BWT1G	BC858	BCM62B
BC848A	BC856S	BC858A	BCM847BS
BC848B	BC856T	BC858AW	BCM847BV
BC848BW	BC856W	BC858B	BCM847DS
BC848CW	BC857	BC858BW	BCM856BS
BC848W	BC857A	BC858C	BCM856DS
BC849B	BC857AM	BC858CW	BCM857BS
BC849BW	BC857AMB	BC858W	BCM857BV
BC849C	BC857AT	BC859A	BCM857DS
BC849CW	BC857AW	BC859B	BCP49
BC850B	BC857B	BC859BW	BCP51
BC850BW	BC857BDW1T1G	BC859C	BCP51-10
BC850C	BC857BM	BC859CW	BCP51-16
BC850CW	BC857BMB	BC860A	BCP52
BC856	BC857BS	BC860B	BCP52-10
BC856A	BC857BT	BC860BW	BCP52-16
BC856ALT1G	BC857BV	BC860C	BCP53
BC856AT	BC857BW	BC860CW	BCP53-10
BC856AW	BC857C	BC868	BCP53-16

# Multisim 14.0 Education Components

---

BCP54	BCR108	BCR146	BCR198S
BCP54-10	BCR108S	BCR148	BCR198W
BCP54-16	BCR108W	BCR148S	BCR22PN
BCP55	BCR10PN	BCR148W	BCR35PN
BCP55-10	BCR112	BCR158	BCR48PN
BCP55-16	BCR112W	BCR158W	BCR503
BCP56	BCR116	BCR162	BCR505
BCP56-10	BCR116S	BCR166	BCR512
BCP56-10T1	BCR116W	BCR166W	BCR521
BCP56-10T1G	BCR119	BCR169	BCR523
BCP56-16	BCR119S	BCR169S	BCR523U
BCP56-16T1	BCR119W	BCR169W	BCR533
BCP56-16T1G	BCR129	BCR183	BCR553
BCP56-16T3G	BCR129W	BCR183S	BCR555
BCP56T1	BCR133	BCR183W	BCR562
BCP56T1G	BCR133S	BCR185	BCR573
BCP56T3G	BCR133W	BCR185S	BCR583
BCP68	BCR135	BCR185W	BCV26
BCP68-25	BCR135S	BCR191	BCV27
BCP68T1G	BCR135W	BCR191W	BCV28
BCP69	BCR141	BCR192	BCV29
BCP69-16	BCR141S	BCR192W	BCV46
BCP69-25	BCR141W	BCR196	BCV47
BCP69T1G	BCR142	BCR196W	BCV48
BCR08PN	BCR142W	BCR198	BCV49

# Multisim 14.0 Education Components

---

BCV61	BCW61A	BCX38B	BCX59VIII
BCV61A	BCW61B	BCX41	BCX59X
BCV61B	BCW61C	BCX42	BCX68
BCV61C	BCW61D	BCX51	BCX69
BCV62	BCW61FF	BCX51-10	BCX70G
BCV62A	BCW61FN	BCX51-16	BCX70H
BCV62B	BCW65A	BCX52	BCX70J
BCV62C	BCW65B	BCX52-10	BCX70K
BCV63	BCW65C	BCX52-16	BCX71G
BCV63B	BCW66F	BCX53	BCX71H
BCV64B	BCW66G	BCX53-10	BCX71J
BCV65	BCW66H	BCX53-16	BCX71K
BCV71	BCW67A	BCX54	BD135
BCV72	BCW68	BCX54-10	BD135-10
BCW29	BCW68F	BCX54-16	BD135-16
BCW30	BCW69	BCX55	BD135G
BCW31	BCW70	BCX55-10	BD136
BCW32	BCW71	BCX55-16	BD136G
BCW33	BCW72	BCX56	BD137
BCW60A	BCW89	BCX56-10	BD137G
BCW60B	BCX17	BCX56-16	BD138
BCW60C	BCX17_25	BCX58IX	BD138G
BCW60D	BCX17LT1G	BCX58VIII	BD139
BCW60FF	BCX18	BCX58X	BD139G
BCW60FN	BCX19	BCX59IX	BD140

# Multisim 14.0 Education Components

---

BD140G	BD676G	BDW47G	BF422G
BD159G	BD677AG	BDX33BG	BF423
BD179G	BD677G	BDX33CG	BF450
BD180G	BD678AG	BDX34BG	BF469
BD234G	BD678G	BDX34CG	BF470
BD237G	BD679AG	BDX53BG	BF471
BD241CG	BD679G	BDX53CG	BF472
BD242BG	BD680AG	BDX54BG	BF510
BD242CG	BD680G	BDX54CG	BF511
BD243CG	BD681G	BF240	BF512
BD244BG	BD682G	BF245A	BF513
BD244CG	BD787G	BF245B	BF517
BD329	BD788G	BF245C	BF545A
BD330	BD809G	BF246A	BF545B
BD436TG	BD810G	BF247A	BF545C
BD437G	BDP947	BF256A	BF550
BD437TG	BDP948	BF256B	BF556A
BD438G	BDP949	BF370R	BF556B
BD439G	BDP950	BF410A	BF570
BD440G	BDP953	BF410B	BF603
BD441G	BDP954	BF410C	BF620
BD442G	BDV64BG	BF410D	BF621
BD675AG	BDV65BG	BF420	BF622
BD675G	BDW42G	BF421	BF623
BD676AG	BDW46G	BF422	BF720

# Multisim 14.0 Education Components

---

BF721	BF908WR	BFN37	BFP490
BF722	BF909	BFN39	BFP81
BF723	BF909R	BFP136W	BFP93A
BF799	BF909WR	BFP180	BFQ31
BF799W	BF998	BFP180W	BFQ81
BF820	BF998R	BFP181	BFR106
BF820W	BF998WR	BFP181W	BFR180
BF821	BFG135A	BFP182	BFR180W
BF822	BFG193	BFP182W	BFR181
BF822W	BFG194	BFP183	BFR181W
BF823	BFG196	BFP183W	BFR182
BF824	BFG19S	BFP193	BFR182W
BF824W	BFG235	BFP193W	BFR183
BF840	BFN16	BFP194	BFR183W
BF851A	BFN17	BFP196	BFR193
BF851B	BFN18	BFP196W	BFR193W
BF851C	BFN19	BFP22	BFR194
BF861A	BFN21	BFP23	BFR280
BF861B	BFN22	BFP25	BFR280W
BF861C	BFN23	BFP26	BFR30
BF869	BFN24	BFP280	BFR31
BF871	BFN25	BFP280W	BFR35AP
BF904	BFN26	BFP405	BFR92ALT1
BF904R	BFN27	BFP420	BFR92P
BF904WR	BFN36	BFP450	BFR92W

# Multisim 14.0 Education Components

---

BFR93A	BFW11	BOSCH-EDC16- BDM-HDR	BSB056N10NN3 G
BFR93ALT1	BFW12	BPASS	BSB165N15NZ3 G
BFR93AW	BFW13	BPV10NF	BSB280N15NZ3 G
BFS17	BFW61	BPV22NF	BSC009NE2LS
BFS17H	BICOLOR_LED_Red/ Green	BPV23F	BSC010N04LS
BFS17LT1	BICOLOR_LED_Red- Orange/Green	BPV23NF	BSC010N04LSI
BFS17P	BIPOLAR_CURRENT	BPW 34	BSC010NE2LS
BFS17S	BIPOLAR_VOLTAGE	BPW 34 FA	BSC010NE2LSI
BFS17W	BJT_LPNP	BPW 34 FAS	BSC011N03LS
BFS18	BJT_NPN	BPW 34 FASR	BSC011N03LSI
BFS19	BJT_NPN_4T	BRUSHLESS_DC_M ACHINE	BSC014N03LS G
BFS20	BJT_NPN_RATED	BRUSHLESS_DC_M ACHINE_HALL	BSC014N03MS G
BFS20W	Bjt_npn1	BS170	BSC014N04LS
BFS480	BJT_PNP	BSB008NE2LX	BSC014N04LSI
BFS481	BJT_PNP_4T	BSB012N03LX3 G	BSC014N06NS
BFS482	BJT_PNP_RATED	BSB012NE2LX	BSC014NE2LSI
BFS483	Bjt-pnp1	BSB012NE2LXI	BSC016N03LS G
BFS60	BOOST_CONVERTE R	BSB013NE2LXI	BSC016N03MS G
BFT46	BOOSTCCM	BSB014N04LX3 G	BSC016N04LS G
BFT92	BOOSTCM	BSB015N04NX3 G	BSC016N06NS
BFT92W	BOOSTDCM	BSB017N03LX3 G	BSC017N04NS G
BFU308	BOOSTVM	BSB028N06NN3 G	BSC018N04LS G
BFU309		BSB044N08NN3 G	BSC018NE2LS
BFU310			BSC018NE2LSI
BFW10			BSC019N02KS G



# Multisim 14.0 Education Components

---

BSC019N04LS	BSC042N03MS G	BSC080N03MS G	BSC100N06LS3 G
BSC019N04NS G	BSC042NE7NS3 G	BSC080P03LS G	BSC100N10NSF G
BSC020N03LS G	BSC046N02KS G	BSC082N10LS G	BSC105N10LSF G
BSC020N03MS G	BSC046N10NS3 G	BSC084P03NS3 G	BSC109N10NS3 G
BSC022N04LS	BSC047N08NS3 G	BSC084P03NS3E G	BSC110N06NS3 G
BSC024NE2LS	BSC050N03LS G	BSC0901NS	BSC118N10NS G
BSC025N03LS G	BSC050N03MS G	BSC0901NSI	BSC120N03LS G
BSC025N03MS G	BSC050N04LS G	BSC0902NS	BSC120N03MS G
BSC026N02KS G	BSC050NE2LS	BSC0902NSI	BSC123N08NS3 G
BSC026N04LS	BSC052N03LS	BSC0904NSI	BSC123N10LS G
BSC027N04LS G	BSC054N04NS G	BSC0906NS	BSC12DN20NS3 G
BSC028N06LS3 G	BSC057N03LS G	BSC0908NS	BSC130P03LS G
BSC028N06NS	BSC057N03MS G	BSC0909NS	BSC150N03LD G
BSC030N03LS G	BSC057N08NS3 G	BSC090N03LS G	BSC152N10NSF G
BSC030N03MS G	BSC059N04LS G	BSC090N03MS G	BSC159N10LSF G
BSC030N04NS G	BSC060N10NS3 G	BSC0910NDI	BSC160N10NS3 G
BSC030P03NS3 G	BSC060P03NS3E G	BSC0911ND	BSC16DN25NS3 G
BSC031N06NS3 G	BSC066N06NS	BSC0921NDI	BSC190N12NS3 G
BSC032N04LS	BSC067N06LS3 G	BSC0923NDI	BSC190N15NS3 G
BSC032NE2LS	BSC070N10NS3 G	BSC0924NDI	BSC196N10NS G
BSC034N06NS	BSC072N03LD G	BSC0925ND	BSC200P03LS G
BSC035N04LS G	BSC076N06NS3 G	BSC093N04LS G	BSC205N10LS G
BSC036NE7NS3 G	BSC077N12NS3 G	BSC097N06NS	BSC22DN20NS3 G
BSC039N06NS	BSC079N10NS G	BSC100N03LS G	BSC240N12NS3 G
BSC042N03LS G	BSC080N03LS G	BSC100N03MS G	BSC252N10NSF G

# Multisim 14.0 Education Components

---

BSC265N10LSF G	BSF450NE7NH3 G	BSL314PE	BSO203SP H
BSC320N20NS3 G	BSH103	BSL606SN	BSO207P H
BSC340N08NS3 G	BSH105	BSL802SN	BSO211P H
BSC360N15NS3 G	BSH108	BSL806N	BSO220N03MD G
BSC440N10NS3 G	BSH111	BSN011NE2LS	BSO220N03MS G
BSC500N20NS3 G	BSH114	BSN011NE2LSI	BSO301SP H
BSC520N15NS3 G	BSH121	BSN012N03LS	BSO303SP H
BSC600N25NS3 G	BSH201	BSN012N03LSI	BSO330N02K G
BSC750N10ND G	BSH202	BSN045NE2LS	BSO613SPV G
BSC900N20NS3 G	BSH203	BSN048N03LS	BSP 60 E6327
BSD214	BSH205	BSN20	BSP030
BSD214SN	BSH207	BSO033N03MS G	BSP100
BSD215	BSJ108	BSO040N03MS G	BSP110
BSD223P	BSJ109	BSO051N03MS G	BSP122
BSD235N	BSJ110	BSO065N03MS G	BSP123
BSD314SPE	BSL202SN	BSO080P03NS3 G	BSP125
BSD316SN	BSL205N	BSO080P03NS3E G	BSP126
BSD816SN	BSL207N	BSO080P03S H	BSP129
BSD840N	BSL207SP	BSO083N03MS G	BSP130
BSE-080-01-L-D-A	BSL211SP	BSO110N03MS G	BSP135
BSF024N03LT3 G	BSL214N	BSO130N03MS G	BSP149
BSF030NE2LQ	BSL302SN	BSO130P03S H	BSP16T1G
BSF035NE2LQ	BSL306N	BSO150N03MD G	BSP170P
BSF050N03LQ3 G	BSL307SP	BSO200P03S H	BSP171P
BSF134N10NJ3 G	BSL308PE	BSO201SP H	BSP19

# Multisim 14.0 Education Components

---

BSP19AT1G	BSP324	BSR316P	BSS138BKW
BSP204	BSP33	BSR33	BSS138LT1G
BSP204A	BSP41	BSR41	BSS138LT3G
BSP205	BSP43	BSR43	BSS138N
BSP206	BSP50	BSR56	BSS138P
BSP220	BSP51	BSR57	BSS138PS
BSP225	BSP52	BSR58	BSS138PW
BSP230	BSP52T1G	BSR606N	BSS138W
BSP250	BSP52T3G	BSR802N	BSS139
BSP295	BSP60	BSR92P	BSS145
BSP296	BSP61	BSS100	BSS159N
BSP297	BSP613P	BSS101	BSS169
BSP299	BSP62	BSS110	BSS192
BSP304	BSP88	BSS119	BSS192P
BSP304A	BSP89	BSS123	BSS205N
BSP31	BSP92P	BSS123LT1G	BSS209PW
BSP315	BSR13	BSS125	BSS214N
BSP315P	BSR14	BSS126	BSS214NW
BSP316	BSR16	BSS127	BSS223PW
BSP316P	BSR19A	BSS129	BSS225
BSP317	BSR202N	BSS131	BSS229
BSP317P	BSR30	BSS135	BSS295
BSP318S	BSR302N	BSS138	BSS296
BSP319	BSR31	BSS138BK	BSS297
BSP32	BSR315P	BSS138BKS	BSS306N

# Multisim 14.0 Education Components

---

BSS308PE	BSS84AKS	BSV236SP	BSZ068N06NS
BSS314PE	BSS84AKT	BSV52	BSZ076N06NS3 G
BSS315P	BSS84AKV	BSV78	BSZ086P03NS3 G
BSS316N	BSS84AKW	BSV79	BSZ086P03NS3E G
BSS606N	BSS84LT1G	BSV80	BSZ088N03LS G
BSS63	BSS84P	BSV81	BSZ088N03MS G
BSS64	BSS84PW	BSZ018NE2LS	BSZ0901NS
BSS670S2L	BSS84PW H6327	BSZ018NE2LSI	BSZ0901NSI
BSS7728N	BSS87	BSZ019N03LS	BSZ0902NS
BSS79B	BSS88	BSZ023N04LS	BSZ0902NSI
BSS79C	BSS89	BSZ028N04LS	BSZ0904NSI
BSS806N	BSS92	BSZ034N04LS	BSZ0907ND
BSS80B	BSS98	BSZ035N03LS G	BSZ0908ND
BSS80C	BST100	BSZ035N03MS G	BSZ0909NS
BSS816NW	BST110	BSZ036NE2LS	BSZ097N04LS G
BSS81B	BST120	BSZ040N04LS G	BSZ100N03LS G
BSS81C	BST122	BSZ042N04NS G	BSZ100N03MS G
BSS82B	BST39	BSZ042N06NS	BSZ100N06LS3 G
BSS82C	BST50	BSZ050N03LS G	BSZ100N06NS
BSS83	BST51	BSZ050N03MS G	BSZ105N04NS G
BSS83P	BST52	BSZ058N03LS G	BSZ110N06NS3 G
BSS84	BST60	BSZ058N03MS G	BSZ120P03NS3 G
BSS84AK	BST61	BSZ060NE2LS	BSZ120P03NS3E G
BSS84AKM	BST62	BSZ065N03LS	BSZ123N08NS3 G
BSS84AKMB	BST82	BSZ067N06LS3 G	BSZ12DN20NS3 G

# Multisim 14.0 Education Components

---

BSZ130N03LS G	BT137	BTW43	BUFFER
BSZ130N03MS G	BT137-E	BTW45_400R	BUH100G
BSZ150N10LS3 G	BT137-F	BTY79_400R	BUH150G
BSZ160N10NS3 G	BT137-G	BTY91_400R	BUH50G
BSZ165N04NS G	BT138	BU323ZG	BUK6207-55C
BSZ16DN25NS3 G	BT138-E	BU406G	BUK6209-30C
BSZ180P03NS3 G	BT138-F	BUB323ZG	BUK6210-55C
BSZ180P03NS3E G	BT138-G	BUB323ZT4G	BUK6211-75C
BSZ22DN20NS3 G	BT139	BUCK_BOOST_CONVERTER	BUK6212-40C
BSZ240N12NS3 G	BT139-E	BUCK_CONVERTER	BUK6213-30C
BSZ340N08NS3 G	BT139-F	BUCKCCM	BUK6215-75C
BSZ42DN25NS3 G	BT139-G	BUCKCM	BUK6217-55C
BSZ440N10NS3 G	BT145_500R	BUCKDCM	BUK6218-40C
BSZ520N15NS3 G	BT148_400R	BUCKVM	BUK6226-75C
BSZ900N15NS3 G	BT148W_400R	BUD42D-1G	BUK6228-55C
BSZ900N20NS3 G	BT149_B	BUD42DT4G	BUK6246-75C
BT134	BT150_500R	BUF	BUK624R5-30C
BT134-E	BT151_500R	BUF_3S_AHOE	BUK625R0-40C
BT134-F	BT152_400R	BUF_3S_ALOE	BUK625R2-30C
BT134-G	BT153_500R	BUF_CO	BUK626R2-40C
BT134W	BT169_B	BUF_INV	BUK6507-55C
BT136	BTA140	BUF601AP	BUK6507-75C
BT136-E	BTW38_600R	BUF602ID	BUK6510-75C
BT136-F	BTW40_400R	BUF602IDBVR	BUK652R1-30C
BT136-G	BTW42_600R		BUK652R6-40C

# Multisim 14.0 Education Components

---

BUK653R3-30C	BUK751R6-30E	BUK7E1R8-40E	BUK7Y153-100E
BUK653R4-40C	BUK751R8-40E	BUK7E1R9-40E	BUK7Y15-60E
BUK653R5-55C	BUK752R3-40E	BUK7E2R3-40E	BUK7Y18-55B
BUK653R7-30C	BUK752R7-60E	BUK7E2R6-60E	BUK7Y18-75B
BUK654R0-75C	BUK753R1-40E	BUK7E3R1-40E	BUK7Y20-30B
BUK654R6-55C	BUK753R5-60E	BUK7E3R5-60E	BUK7Y21-40E
BUK654R8-40C	BUK753R8-80E	BUK7E4R0-80E	BUK7Y22-100E
BUK655R0-75C	BUK754R0-40C	BUK7E4R6-60E	BUK7Y25-40B
BUK6607-55C	BUK754R7-60E	BUK7E5R2-100E	BUK7Y25-60E
BUK6607-75C	BUK755R4-100E	BUK7E8R3-40E	BUK7Y25-80E
BUK6610-75C	BUK758R3-40E	BUK7K25-40E	BUK7Y28-75B
BUK661R8-30C	BUK7613-100E	BUK7K5R1-30E	BUK7Y29-40E
BUK661R9-40C	BUK761R3-30E	BUK7K5R6-30E	BUK7Y35-55B
BUK662R4-40C	BUK761R4-30E	BUK7K6R8-40E	BUK7Y38-100E
BUK662R5-30C	BUK761R5-40E	BUK7Y07-30B	BUK7Y41-80E
BUK662R7-55C	BUK761R6-40E	BUK7Y08-40B	BUK7Y43-60E
BUK663R2-40C	BUK762R4-60E	BUK7Y102-100B	BUK7Y4R4-40E
BUK663R5-30C	BUK7631-100E	BUK7Y10-30B	BUK7Y4R8-60E
BUK663R5-55C	BUK763R8-80E	BUK7Y113-100E	BUK7Y53-100B
BUK663R7-75C	BUK764R2-80E	BUK7Y12-100E	BUK7Y54-75B
BUK664R4-55C	BUK765R0-100E	BUK7Y12-40E	BUK7Y59-60E
BUK664R6-40C	BUK768R1-100E	BUK7Y12-55B	BUK7Y65-100E
BUK6C2R1-55C	BUK769R6-80E	BUK7Y13-40B	BUK7Y6R0-60E
BUK6C3R3-75C	BUK7E13-60E	BUK7Y14-80E	BUK7Y72-80E
BUK7514-60E	BUK7E1R6-30E	BUK7Y15-100E	BUK7Y7R6-40E

# Multisim 14.0 Education Components

---

BUK7Y7R8-80E	BUK9E1R6-30E	BUK9Y14-40B	BUK9Y65-100E
BUK7Y8R7-60E	BUK9E2R3-40E	BUK9Y14-80E	BUK9Y6R0-60E
BUK7Y98-80E	BUK9E2R8-60E	BUK9Y15-100E	BUK9Y72-80E
BUK7Y9R9-80E	BUK9E3R7-60E	BUK9Y153-100E	BUK9Y7R6-40E
BUK9515-60E	BUK9E4R4-80E	BUK9Y15-60E	BUK9Y8R5-80E
BUK951R6-30E	BUK9E4R9-60E	BUK9Y19-55B	BUK9Y8R7-60E
BUK951R9-40E	BUK9E6R1-100E	BUK9Y19-75B	BUL45D2G
BUK952R3-40E	BUK9E8R5-40E	BUK9Y21-40E	BUL45G
BUK952R8-60E	BUK9K18-40E	BUK9Y22-100E	BUV21G
BUK953R2-40E	BUK9K29-100E	BUK9Y22-30B	BUV22G
BUK953R5-60E	BUK9K35-60E	BUK9Y25-60E	BUV26G
BUK954R4-80E	BUK9K45-100E	BUK9Y25-80E	BUX85G
BUK958R5-40E	BUK9K52-60E	BUK9Y27-40B	BUZ10
BUK9611-80E	BUK9K6R2-40E	BUK9Y29-40E	BUZ100
BUK9615-100E	BUK9K89-100E	BUK9Y30-75B	BUZ101
BUK961R4-30E	BUK9Y07-30B	BUK9Y38-100E	BUZ102
BUK961R5-30E	BUK9Y09-40B	BUK9Y3R0-40E	BUZ104
BUK961R6-40E	BUK9Y104-100B	BUK9Y40-55B	BUZ10L
BUK962R5-60E	BUK9Y107-80E	BUK9Y41-80E	BUZ10M
BUK9637-100E	BUK9Y11-30B	BUK9Y43-60E	BUZ11GE
BUK964R2-80E	BUK9Y113-100E	BUK9Y4R4-40E	BUZ12
BUK964R7-80E	BUK9Y11-80E	BUK9Y4R8-60E	BUZ12AL
BUK965R8-100E	BUK9Y12-100E	BUK9Y53-100B	BUZ171
BUK969R3-100E	BUK9Y12-40E	BUK9Y58-75B	BUZ173
BUK9E15-60E	BUK9Y12-55B	BUK9Y59-60E	BUZ20

# Multisim 14.0 Education Components

---

BUZ21	BUZ40B	BUZ90	BY718
BUZ22	BUZ41A	BUZ91A	BY719
BUZ220	BUZ45B	BUZ92	BY720
BUZ271	BUZ50B	BUZZER	BY721
BUZ272	BUZ51	BVSS123LT1G	BY722
BUZ305	BUZ53A	BVSS138LT1G	BY723
BUZ30A	BUZ60	BY228	BYD11
BUZ31	BUZ61A	BY328	BYD11D
BUZ310	BUZ64	BY438	BYD11G
BUZ311	BUZ70	BY448	BYD11J
BUZ323	BUZ71	BY458	BYD11K
BUZ325	BUZ71L	BY505	BYD11M
BUZ326	BUZ71LGE	BY527	BYD13D
BUZ331	BUZ72	BY584	BYD13G
BUZ334	BUZ72GE	BY627	BYD13J
BUZ338	BUZ73	BY705	BYD13K
BUZ341	BUZ73AGE	BY706	BYD13M
BUZ342	BUZ73L	BY710	BYD14D
BUZ342KL	BUZ74A	BY711	BYD14G
BUZ344	BUZ76	BY712	BYD14J
BUZ345	BUZ77A	BY713	BYD14K
BUZ346	BUZ78	BY714	BYD14M
BUZ350	BUZ80A	BY715	BYD17D
BUZ356	BUZ81	BY716	BYD17G
BUZ358	BUZ84A	BY717	BYD17J



# Multisim 14.0 Education Components

---

BYD17K	BYD73F	BYM10-200	BYM56A
BYD17M	BYD73G	BYM10-400	BYM56B
BYD31D	BYD74A	BYM10-50	BYM56C
BYD31G	BYD74B	BYM10-600	BYM56D
BYD31J	BYD74C	BYM10-800	BYM56E
BYD33D	BYD74D	BYM11-100	BYS10-45-E3/TR
BYD33G	BYD74E	BYM11-1000	BYS11-90-E3/TR
BYD33J	BYD74F	BYM11-1000-E3/96	BYT28-300-E3/45
BYD33K	BYD74G	BYM11-100-E3/96	BYV10-20
BYD33M	BYD77A	BYM11-200	BYV10-30
BYD34D	BYD77B	BYM11-400	BYV10-40
BYD34G	BYD77C	BYM11-50	BYV26A
BYD34J	BYD77D	BYM11-600	BYV26B
BYD34K	BYD77E	BYM11-800	BYV26C
BYD34M	BYD77F	BYM12-400-E3/96	BYV26D
BYD37D	BYD77G	BYM26A	BYV26E
BYD37G	BYG10G-E3/TR	BYM26B	BYV27-100
BYD37J	BYG10J-E3/TR	BYM26C	BYV27-50
BYD37K	BYG20J-E3/TR	BYM26D	BYV28-100
BYD37M	BYG21M-E3/TR	BYM26E	BYV28-150
BYD73A	BYG22D-E3/TR	BYM36A	BYV28-200
BYD73B	BYG24J-E3/TR3	BYM36B	BYV28-50
BYD73C	BYM10-100	BYM36C	BYV32-200G
BYD73D	BYM10-1000	BYM36D	BYV36A
BYD73E	BYM10-1000-E3/97	BYM36E	BYV36B

# Multisim 14.0 Education Components

---

BYV36C	BZA462A	BZB784-C3V0	BZB84-B2V7
BYV36D	BZA820A	BZB784-C3V3	BZB84-B30
BYV36E	BZA856A	BZB784-C3V6	BZB84-B33
BYV95A	BZA856AL	BZB784-C3V9	BZB84-B36
BYV95B	BZA856AVL	BZB784-C4V3	BZB84-B39
BYV95C	BZA862A	BZB784-C4V7	BZB84-B3V0
BYV96D	BZA862AL	BZB784-C5V1	BZB84-B3V3
BYV96E	BZA862AVL	BZB784-C5V6	BZB84-B3V6
BYW29-200G	BZA868A	BZB784-C6V2	BZB84-B3V9
BYW51-200G	BZA868AL	BZB784-C6V8	BZB84-B43
BYW54	BZA868AVL	BZB784-C7V5	BZB84-B47
BYW55	BZA956A	BZB784-C8V2	BZB84-B4V3
BYW56	BZA956AVL	BZB784-C9V1	BZB84-B4V7
BYW80-200G	BZA962A	BZB84-B10	BZB84-B51
BYW95A	BZA962AVL	BZB84-B11	BZB84-B56
BYW95B	BZA968A	BZB84-B12	BZB84-B5V1
BYW95C	BZA968AVL	BZB84-B13	BZB84-B5V6
BYW96D	BZB100A	BZB84-B15	BZB84-B62
BYW96E	BZB784-C10	BZB84-B16	BZB84-B68
BYX10G	BZB784-C11	BZB84-B18	BZB84-B6V2
BYX110GP	BZB784-C12	BZB84-B20	BZB84-B6V8
BZA408B	BZB784-C13	BZB84-B22	BZB84-B75
BZA418A	BZB784-C15	BZB84-B24	BZB84-B7V5
BZA420A	BZB784-C2V4	BZB84-B27	BZB84-B8V2
BZA456A	BZB784-C2V7	BZB84-B2V4	BZB84-B9V1

# Multisim 14.0 Education Components

---

BZB84-C10	BZB84-C51	BZB984-C5V1	BZT52H-B43
BZB84-C11	BZB84-C56	BZB984-C5V6	BZT52H-B47
BZB84-C12	BZB84-C5V1	BZB984-C6V2	BZT52H-B51
BZB84-C13	BZB84-C5V6	BZB984-C6V8	BZT52H-B56
BZB84-C15	BZB84-C62	BZB984-C7V5	BZT52H-B5V1
BZB84-C16	BZB84-C68	BZB984-C8V2	BZT52H-B5V6
BZB84-C18	BZB84-C6V2	BZB984-C9V1	BZT52H-B62
BZB84-C20	BZB84-C6V8	BZT52H-B10	BZT52H-B68
BZB84-C22	BZB84-C75	BZT52H-B11	BZT52H-B6V2
BZB84-C24	BZB84-C7V5	BZT52H-B12	BZT52H-B6V8
BZB84-C27	BZB84-C8V2	BZT52H-B13	BZT52H-B75
BZB84-C2V4	BZB84-C9V1	BZT52H-B15	BZT52H-B7V5
BZB84-C2V7	BZB984-C10	BZT52H-B16	BZT52H-B8V2
BZB84-C30	BZB984-C11	BZT52H-B18	BZT52H-B9V1
BZB84-C33	BZB984-C12	BZT52H-B20	BZT52H-C10
BZB84-C36	BZB984-C13	BZT52H-B22	BZT52H-C11
BZB84-C39	BZB984-C15	BZT52H-B24	BZT52H-C12
BZB84-C3V0	BZB984-C2V4	BZT52H-B27	BZT52H-C13
BZB84-C3V3	BZB984-C2V7	BZT52H-B2V4	BZT52H-C15
BZB84-C3V6	BZB984-C3V0	BZT52H-B2V7	BZT52H-C16
BZB84-C3V9	BZB984-C3V3	BZT52H-B30	BZT52H-C18
BZB84-C43	BZB984-C3V6	BZT52H-B33	BZT52H-C20
BZB84-C47	BZB984-C3V9	BZT52H-B36	BZT52H-C22
BZB84-C4V3	BZB984-C4V3	BZT52H-B39	BZT52H-C24
BZB84-C4V7	BZB984-C4V7	BZT52H-B3V0	BZT52H-C27

# Multisim 14.0 Education Components

---

BZT52H-C2V4	BZV49-C12	BZV55-B47	BZV55-C3V0
BZT52H-C2V7	BZV49-C16	BZV55-B4V3	BZV55-C3V3
BZT52H-C30	BZV49-C3V6	BZV55-B4V7	BZV55-C3V6
BZT52H-C33	BZV55-B10	BZV55-B51	BZV55-C3V9
BZT52H-C36	BZV55-B11	BZV55-B56	BZV55-C43
BZT52H-C39	BZV55-B12	BZV55-B5V1	BZV55-C47
BZT52H-C3V0	BZV55-B13	BZV55-B5V6	BZV55-C4V3
BZT52H-C3V6	BZV55-B15	BZV55-B68	BZV55-C4V7
BZT52H-C3V9	BZV55-B16	BZV55-B6V2	BZV55-C5V1
BZT52H-C43	BZV55-B18	BZV55-B6V8	BZV55-C5V6
BZT52H-C47	BZV55-B20	BZV55-B75	BZV55-C6V2
BZT52H-C4V3	BZV55-B22	BZV55-B7V5	BZV55-C6V8
BZT52H-C4V7	BZV55-B24	BZV55-B8V2	BZV55-C7V5
BZT52H-C51	BZV55-B27	BZV55-B9V1	BZV55-C8V2
BZT52H-C56	BZV55-B2V4	BZV55-C10	BZV55-C9V1
BZT52H-C5V1	BZV55-B2V7	BZV55-C11	BZV55-F2V4
BZT52H-C5V6	BZV55-B30	BZV55-C12	BZV60-B10
BZT52H-C62	BZV55-B33	BZV55-C13	BZV60-B11
BZT52H-C68	BZV55-B36	BZV55-C15	BZV60-B12
BZT52H-C6V2	BZV55-B39	BZV55-C16	BZV60-B13
BZT52H-C6V8	BZV55-B3V0	BZV55-C18	BZV60-B15
BZT52H-C75	BZV55-B3V3	BZV55-C27	BZV60-B16
BZT52H-C7V5	BZV55-B3V6	BZV55-C2V4	BZV60-B18
BZT52H-C8V2	BZV55-B3V9	BZV55-C2V7	BZV60-B20
BZT52H-C9V1	BZV55-B43	BZV55-C33	BZV60-B22

# Multisim 14.0 Education Components

---

BZV60-B24	BZV60-B7V5	BZV60-C47	BZV85-C24
BZV60-B27	BZV60-B8V2	BZV60-C4V3	BZV85-C27
BZV60-B2V4	BZV60-B9V1	BZV60-C4V7	BZV85-C30
BZV60-B2V7	BZV60-C10	BZV60-C51	BZV85-C33
BZV60-B30	BZV60-C11	BZV60-C56	BZV85-C36
BZV60-B33	BZV60-C12	BZV60-C5V1	BZV85-C39
BZV60-B36	BZV60-C13	BZV60-C5V6	BZV85-C3V6
BZV60-B39	BZV60-C15	BZV60-C62	BZV85-C3V9
BZV60-B3V0	BZV60-C16	BZV60-C68	BZV85-C43
BZV60-B3V3	BZV60-C18	BZV60-C6V2	BZV85-C47
BZV60-B3V6	BZV60-C20	BZV60-C6V8	BZV85-C4V3
BZV60-B3V9	BZV60-C22	BZV60-C75	BZV85-C4V7
BZV60-B43	BZV60-C24	BZV60-C7V5	BZV85-C51
BZV60-B47	BZV60-C27	BZV60-C8V2	BZV85-C5V1
BZV60-B4V3	BZV60-C2V4	BZV60-C9V1	BZV85-C5V6
BZV60-B4V7	BZV60-C2V7	BZV80	BZV85-C62
BZV60-B51	BZV60-C30	BZV85-C10	BZV85-C68
BZV60-B56	BZV60-C33	BZV85-C11	BZV85-C6V2
BZV60-B5V1	BZV60-C36	BZV85-C12	BZV85-C6V8
BZV60-B5V6	BZV60-C39	BZV85-C13	BZV85-C75
BZV60-B62	BZV60-C3V0	BZV85-C15	BZV85-C7V5
BZV60-B68	BZV60-C3V3	BZV85-C16	BZV85-C8V2
BZV60-B6V2	BZV60-C3V6	BZV85-C18	BZV86-1V4
BZV60-B6V8	BZV60-C3V9	BZV85-C20	BZV86-2V0
BZV60-B75	BZV60-C43	BZV85-C22	BZV86-2V6

# Multisim 14.0 Education Components

---

BZV86-3V2	BZV90-C4V7	BZW03-C18	BZW03-C9V1
BZV90-C10	BZV90-C51	BZW03-C180	BZX100A
BZV90-C11	BZV90-C56	BZW03-C20	BZX384-B10
BZV90-C12	BZV90-C5V1	BZW03-C200	BZX384-B11
BZV90-C13	BZV90-C5V6	BZW03-C22	BZX384-B12
BZV90-C15	BZV90-C62	BZW03-C220	BZX384-B13
BZV90-C16	BZV90-C68	BZW03-C24	BZX384-B15
BZV90-C18	BZV90-C6V2	BZW03-C240	BZX384-B16
BZV90-C20	BZV90-C6V8	BZW03-C27	BZX384-B18
BZV90-C22	BZV90-C75	BZW03-C270	BZX384-B20
BZV90-C24	BZV90-C7V5	BZW03-C30	BZX384-B22
BZV90-C27	BZV90-C8V2	BZW03-C33	BZX384-B24
BZV90-C2V4	BZV90-C9V1	BZW03-C36	BZX384-B27
BZV90-C2V7	BZW03-C10	BZW03-C39	BZX384-B2V4
BZV90-C30	BZW03-C100	BZW03-C43	BZX384-B2V7
BZV90-C33	BZW03-C11	BZW03-C47	BZX384-B30
BZV90-C36	BZW03-C110	BZW03-C51	BZX384-B33
BZV90-C39	BZW03-C12	BZW03-C56	BZX384-B36
BZV90-C3V0	BZW03-C120	BZW03-C62	BZX384-B39
BZV90-C3V3	BZW03-C13	BZW03-C68	BZX384-B3V0
BZV90-C3V6	BZW03-C130	BZW03-C75	BZX384-B3V3
BZV90-C3V9	BZW03-C15	BZW03-C7V5	BZX384-B3V6
BZV90-C43	BZW03-C150	BZW03-C82	BZX384-B3V9
BZV90-C47	BZW03-C16	BZW03-C8V2	BZX384-B43
BZV90-C4V3	BZW03-C160	BZW03-C91	BZX384-B47

# Multisim 14.0 Education Components

---

BZX384-B4V3	BZX384-C33	BZX55C13	BZX55C5V6
BZX384-B4V7	BZX384-C36	BZX55C15	BZX55C62
BZX384-B51	BZX384-C39	BZX55C16	BZX55C68
BZX384-B56	BZX384-C3V0	BZX55C18	BZX55C6V2
BZX384-B5V1	BZX384-C3V3	BZX55C20	BZX55C6V8
BZX384-B5V6	BZX384-C3V6	BZX55C22	BZX55C75
BZX384-B62	BZX384-C3V9	BZX55C24	BZX55C7V5
BZX384-B68	BZX384-C43	BZX55C27	BZX55C82
BZX384-B6V2	BZX384-C47	BZX55C2V4	BZX55C8V2
BZX384-B6V8	BZX384-C4V3	BZX55C2V7	BZX55C91
BZX384-B75	BZX384-C4V7	BZX55C30	BZX55C9V1
BZX384-B7V5	BZX384-C51	BZX55C33	BZX585-B10
BZX384-B8V2	BZX384-C56	BZX55C36	BZX585-B11
BZX384-B9V1	BZX384-C5V1	BZX55C39	BZX585-B12
BZX384-C10	BZX384-C62	BZX55C3V0	BZX585-B13
BZX384-C11	BZX384-C68	BZX55C3V3	BZX585-B15
BZX384-C12	BZX384-C6V2	BZX55C3V6	BZX585-B16
BZX384-C13	BZX384-C6V8	BZX55C3V9	BZX585-B18
BZX384-C16	BZX384-C75	BZX55C43	BZX585-B20
BZX384-C20	BZX384-C7V5	BZX55C47	BZX585-B22
BZX384-C22	BZX384-C8V2	BZX55C4V3	BZX585-B24
BZX384-C24	BZX384-C9V1	BZX55C4V7	BZX585-B27
BZX384-C2V4	BZX55C10	BZX55C51	BZX585-B2V4
BZX384-C2V7	BZX55C11	BZX55C56	BZX585-B2V7
BZX384-C30	BZX55C12	BZX55C5V1	BZX585-B30

# Multisim 14.0 Education Components

---

BZX585-B33	BZX585-C12	BZX585-C6V2	BZX79-A3V9
BZX585-B36	BZX585-C13	BZX585-C6V8	BZX79-A40
BZX585-B39	BZX585-C16	BZX585-C75	BZX79-A43
BZX585-B3V0	BZX585-C20	BZX585-C7V5	BZX79-A47
BZX585-B3V3	BZX585-C22	BZX585-C8V2	BZX79-A4V3
BZX585-B3V6	BZX585-C24	BZX585-C9V1	BZX79-A4V7
BZX585-B3V9	BZX585-C2V4	BZX79-A10	BZX79-A51
BZX585-B43	BZX585-C2V7	BZX79-A11	BZX79-A56
BZX585-B47	BZX585-C30	BZX79-A12	BZX79-A5V1
BZX585-B4V3	BZX585-C33	BZX79-A13	BZX79-A5V6
BZX585-B4V7	BZX585-C36	BZX79-A15	BZX79-A62
BZX585-B51	BZX585-C39	BZX79-A16	BZX79-A68
BZX585-B56	BZX585-C3V0	BZX79-A18	BZX79-A6V2
BZX585-B5V1	BZX585-C3V3	BZX79-A20	BZX79-A6V8
BZX585-B5V6	BZX585-C3V6	BZX79-A22	BZX79-A75
BZX585-B62	BZX585-C3V9	BZX79-A24	BZX79-A7V5
BZX585-B68	BZX585-C43	BZX79-A27	BZX79-A8V2
BZX585-B6V2	BZX585-C47	BZX79-A2V4	BZX79-A9V1
BZX585-B6V8	BZX585-C4V3	BZX79-A2V7	BZX79-B10
BZX585-B75	BZX585-C4V7	BZX79-A30	BZX79-B11
BZX585-B7V5	BZX585-C51	BZX79-A33	BZX79-B12
BZX585-B8V2	BZX585-C56	BZX79-A36	BZX79-B13
BZX585-B9V1	BZX585-C5V1	BZX79-A3V0	BZX79-B15
BZX585-C10	BZX585-C62	BZX79-A3V3	BZX79-B16
BZX585-C11	BZX585-C68	BZX79-A3V6	BZX79-B18



# Multisim 14.0 Education Components

---

BZX79-B20	BZX79-B7V5	BZX79-C33	BZX83-C10
BZX79-B22	BZX79-B8V2	BZX79-C36	BZX83-C11
BZX79-B24	BZX79-B9V1	BZX79-C39	BZX83-C12
BZX79-B27	BZX79-C10	BZX79-C3V0	BZX83-C13
BZX79-B2V4	BZX79-C100	BZX79-C3V3	BZX83-C15
BZX79-B2V7	BZX79-C11	BZX79-C3V6	BZX83-C16
BZX79-B30	BZX79-C110	BZX79-C3V9	BZX83-C18
BZX79-B33	BZX79-C12	BZX79-C43	BZX83-C20
BZX79-B36	BZX79-C120	BZX79-C47	BZX83-C22
BZX79-B39	BZX79-C13	BZX79-C4V3	BZX83-C24
BZX79-B3V3	BZX79-C130	BZX79-C4V7	BZX83-C27
BZX79-B3V6	BZX79-C15	BZX79-C51	BZX83-C2V7
BZX79-B3V9	BZX79-C150	BZX79-C56	BZX83-C30
BZX79-B43	BZX79-C16	BZX79-C5V1	BZX83-C33
BZX79-B47	BZX79-C160	BZX79-C5V6	BZX83-C3V0
BZX79-B4V3	BZX79-C18	BZX79-C62	BZX83-C3V3
BZX79-B4V7	BZX79-C180	BZX79-C68	BZX83-C3V6
BZX79-B51	BZX79-C20	BZX79-C6V2	BZX83-C3V9
BZX79-B56	BZX79-C200	BZX79-C6V8	BZX83-C4V3
BZX79-B5V1	BZX79-C22	BZX79-C75	BZX83-C4V7
BZX79-B62	BZX79-C24	BZX79-C7V5	BZX83-C5V1
BZX79-B68	BZX79-C27	BZX79-C82	BZX83-C5V6
BZX79-B6V2	BZX79-C2V4	BZX79-C8V2	BZX83-C6V2
BZX79-B6V8	BZX79-C2V7	BZX79-C91	BZX83-C6V8
BZX79-B75	BZX79-C30	BZX79-C9V1	BZX83-C7V5

# Multisim 14.0 Education Components

---

BZX83-C8V2	BZX84-A4V3	BZX84-B27	BZX84B6V2LT1G
BZX83-C9V1	BZX84-A4V7	BZX84-B2V4	BZX84-B6V8
BZX84-A10	BZX84-A51	BZX84-B2V7	BZX84B6V8LT1G
BZX84-A11	BZX84-A56	BZX84-B30	BZX84-B75
BZX84-A12	BZX84-A5V1	BZX84-B33	BZX84-B7V5
BZX84-A13	BZX84-A5V6	BZX84-B36	BZX84B7V5LT1G
BZX84-A15	BZX84-A62	BZX84-B39	BZX84-B8V2
BZX84-A16	BZX84-A68	BZX84-B3V0	BZX84B8V2LT1G
BZX84-A18	BZX84-A6V2	BZX84-B3V3	BZX84-B9V1
BZX84-A20	BZX84-A6V8	BZX84-B3V6	BZX84B9V1LT1G
BZX84-A22	BZX84-A75	BZX84-B3V9	BZX84-C10
BZX84-A24	BZX84-A7V5	BZX84-B43	BZX84-C11
BZX84-A27	BZX84-A8V2	BZX84-B47	BZX84-C12
BZX84-A2V4	BZX84-A9V1	BZX84-B4V3	BZX84C12LT1G
BZX84-A2V7	BZX84-B10	BZX84-B4V7	BZX84-C13
BZX84-A30	BZX84-B11	BZX84B4V7LT1G	BZX84-C15
BZX84-A33	BZX84-B12	BZX84-B51	BZX84C15LT1
BZX84-A36	BZX84-B13	BZX84-B56	BZX84C15LT1G
BZX84-A39	BZX84-B15	BZX84-B5V1	BZX84C15LT3G
BZX84-A3V0	BZX84-B16	BZX84B5V1LT1G	BZX84-C16
BZX84-A3V3	BZX84B16LT1G	BZX84-B5V6	BZX84-C18
BZX84-A3V6	BZX84-B18	BZX84B5V6LT1G	BZX84-C20
BZX84-A3V9	BZX84-B20	BZX84-B62	BZX84-C22
BZX84-A43	BZX84-B22	BZX84-B68	BZX84-C24
BZX84-A47	BZX84-B24	BZX84-B6V2	BZX84-C27

# Multisim 14.0 Education Components

---

BZX84-C2V4	BZX84-C5V6	BZX84J-B15	BZX84J-B62
BZX84-C2V7	BZX84C5V6LT1G	BZX84J-B16	BZX84J-B68
BZX84-C30	BZX84C5V6LT3G	BZX84J-B18	BZX84J-B6V2
BZX84-C33	BZX84-C62	BZX84J-B20	BZX84J-B6V8
BZX84C33LT1G	BZX84-C68	BZX84J-B22	BZX84J-B75
BZX84C33LT3G	BZX84C68LT1G	BZX84J-B24	BZX84J-B7V5
BZX84-C36	BZX84-C6V2	BZX84J-B27	BZX84J-B8V2
BZX84C36LT1G	BZX84C6V2LT1G	BZX84J-B2V4	BZX84J-B9V1
BZX84-C39	BZX84C6V2LT3G	BZX84J-B2V7	BZX84J-C10
BZX84-C3V0	BZX84-C6V8	BZX84J-B30	BZX84J-C11
BZX84C3V0LT1G	BZX84C6V8LT1G	BZX84J-B33	BZX84J-C12
BZX84-C3V3	BZX84C6V8LT3G	BZX84J-B36	BZX84J-C13
BZX84-C3V6	BZX84-C75	BZX84J-B39	BZX84J-C15
BZX84-C3V9	BZX84C75LT1G	BZX84J-B3V0	BZX84J-C16
BZX84-C43	BZX84-C7V5	BZX84J-B3V3	BZX84J-C18
BZX84-C47	BZX84C7V5LT1G	BZX84J-B3V6	BZX84J-C20
BZX84-C4V3	BZX84-C8V2	BZX84J-B3V9	BZX84J-C22
BZX84-C4V7	BZX84C8V2LT1G	BZX84J-B43	BZX84J-C24
BZX84C4V7LT1G	BZX84-C9V1	BZX84J-B47	BZX84J-C27
BZX84C4V7LT3G	BZX84C9V1LT1G	BZX84J-B4V3	BZX84J-C2V4
BZX84-C51	BZX84C9V1LT3G	BZX84J-B4V7	BZX84J-C2V7
BZX84-C56	BZX84J-B10	BZX84J-B51	BZX84J-C30
BZX84-C5V1	BZX84J-B11	BZX84J-B56	BZX84J-C33
BZX84C5V1LT1G	BZX84J-B12	BZX84J-B5V1	BZX84J-C36
BZX84C5V1LT3G	BZX84J-B13	BZX84J-B5V6	BZX84J-C39

# Multisim 14.0 Education Components

---

BZX84J-C3V0	BZX85-C15	BZX85-C6V8	BZX884-B3V3
BZX84J-C3V3	BZX85-C16	BZX85-C75	BZX884-B3V6
BZX84J-C3V6	BZX85-C18	BZX85-C7V5	BZX884-B3V9
BZX84J-C3V9	BZX85-C20	BZX85-C82	BZX884-B43
BZX84J-C43	BZX85-C22	BZX85-C8V2	BZX884-B47
BZX84J-C47	BZX85-C24	BZX85-C91	BZX884-B4V3
BZX84J-C4V3	BZX85-C27	BZX85-C9V1	BZX884-B4V7
BZX84J-C4V7	BZX85-C30	BZX884-B10	BZX884-B51
BZX84J-C51	BZX85-C33	BZX884-B11	BZX884-B56
BZX84J-C56	BZX85-C36	BZX884-B12	BZX884-B5V1
BZX84J-C5V1	BZX85-C39	BZX884-B13	BZX884-B5V6
BZX84J-C5V6	BZX85-C3V3	BZX884-B15	BZX884-B62
BZX84J-C62	BZX85-C3V6	BZX884-B16	BZX884-B68
BZX84J-C68	BZX85-C3V9	BZX884-B18	BZX884-B6V2
BZX84J-C6V2	BZX85-C43	BZX884-B20	BZX884-B6V8
BZX84J-C6V8	BZX85-C47	BZX884-B22	BZX884-B75
BZX84J-C75	BZX85-C4V3	BZX884-B24	BZX884-B7V5
BZX84J-C7V5	BZX85-C4V7	BZX884-B27	BZX884-B8V2
BZX84J-C8V2	BZX85-C51	BZX884-B2V4	BZX884-B9V1
BZX84J-C9V1	BZX85-C56	BZX884-B2V7	BZX884-C10
BZX85-C10	BZX85-C5V1	BZX884-B30	BZX884-C11
BZX85-C100	BZX85-C5V6	BZX884-B33	BZX884-C12
BZX85-C11	BZX85-C62	BZX884-B36	BZX884-C13
BZX85-C12	BZX85-C68	BZX884-B39	BZX884-C16
BZX85-C13	BZX85-C6V2	BZX884-B3V0	BZX884-C20

# Multisim 14.0 Education Components

---

BZX884-C22	C232A	CA0324E	CA3080AE
BZX884-C24	C232B	CA0324M	CA3080AM
BZX884-C2V4	C232D	CA0358AE	CA3080E
BZX884-C2V7	C232F	CA0358AM	CA3080M
BZX884-C30	C232M	CA0358AT	CA3094AE
BZX884-C33	C233A	CA0358E	CA3094AM
BZX884-C36	C233B	CA0358M	CA3094AT
BZX884-C3V0	C233D	CA0358T	CA3094BE
BZX884-C3V3	C233F	CA0741E	CA3094BM
BZX884-C3V6	C233M	CA0741T	CA3094BT
BZX884-C3V9	CA0124E	CA1458E	CA3094E
BZX884-C43	CA0124M	CA1458T	CA3094M
BZX884-C47	CA0158AE	CA2902M	CA3094T
BZX884-C4V3	CA0158AT	CA2902N	CA3100E
BZX884-C4V7	CA0158E	CA2904E	CA3100M
BZX884-C51	CA0158M	CA2904M	CA3100T
BZX884-C56	CA0158T	CA3060E	CA3130E
BZX884-C5V1	CA0224E	CA3078AE	CA3130M
BZX884-C62	CA0224M	CA3078AM	CA3130T
BZX884-C68	CA0258AE	CA3078AT	CA3140E
BZX884-C6V2	CA0258AM	CA3078E	CA3140M
BZX884-C75	CA0258AT	CA3078M	CA3140T
BZX884-C7V5	CA0258E	CA3078T	CA3160E
BZX884-C8V2	CA0258M	CA3080	CA3160T
BZX884-C9V1	CA0258T	CA3080A	CA3193AE

# Multisim 14.0 Education Components

---

CA3193AT	CA5420E	CLC200A8C	CLC404AID
CA3193E	CA5420M	CLC200AI	CLC404AJE
CA3193T	CA5420T	CLC200AK	CLC404AJM5
CA3240AE	CA5470E	CLC200AM	CLC404AJP
CA3240AE1	CA5470M	CLC201	CLC405A8B
CA3240E	CAP_ELECTROLIT_VIRTUAL	CLC203	CLC405AIB
CA3240E1		CLC220	CLC405AJE
CA3260E	CAPACITOR_POL_RATED	CLC400A8B	CLC405AJP
CA3260T	CAPACITOR_RATED	CLC400A8D	CLC406A8B
CA3280E	CAPACITOR_VIRTUAL	CLC400AIB	CLC406A8D
CA3440AE		CLC400AID	CLC406AJE
CA3440M	Capacitor1_100uF	CLC400AJE	CLC406AJM5
CA3450E	Capacitor2_10pF	CLC400AJP	CLC406AJP
CA5130AE	Capacitor3_100pF	CLC401A8B	CLC407AIB
CA5130AM	CCM-DCM1	CLC401A8D	CLC407AJE
CA5130AT	CCM-DCM2	CLC401AIB	CLC407AJP
CA5130E	CD4538BCM	CLC401AID	CLC409A8D
CA5130M	CD4538BCN	CLC401AJE	CLC409AID
CA5130T	CD4538BCWM	CLC401AJP	CLC409AJE
CA5160AE	CHIRP_CURRENT	CLC402A8B	CLC409AJM5
CA5160AM	CHIRP_VOLTAGE	CLC402A8D	CLC409AJP
CA5260AE	CLC103AI	CLC402AID	CLC410A8B
CA5260AM	CLC103AM	CLC402AJE	CLC410A8D
CA5260E	CLC111AJE	CLC402AJP	CLC410AJE
CA5260M	CLC111AJP	CLC404A8D	CLC410AJP

# Multisim 14.0 Education Components

---

CLC411A8B	CLC420B8D	CLC432AJP	CNTR_4BIN_AS
CLC411AJE	CLC420BIB	CLC440A8B	CNTR_4BIN_ASCLR
CLC411AJP	CLC420BJE	CLC440AJE	CNTR_4BIN_S
CLC412A8B	CLC420BJP	CLC440AJP	CNTR_4BIN_SU_D
CLC412AIB	CLC423AJE	CLC449A8B	CNTR_4BINS_DC
CLC412AJE	CLC423AJP	CLC449AJE	CNTR_4SBIN
CLC412AJP	CLC425A8B	CLC449AJP	CNTR_4SDEC
CLC414A8B	CLC425AIB	CLC501A8D	CNTR_7BIN
CLC414A8D	CLC425AJE	CLC501AID	CNTR_8SBIN
CLC414AJE	CLC425AJP	CLC501AJE	CNTR_BCD_S
CLC414AJP	CLC426A8B	CLC501AJP	CNTR_BCD_SDC
CLC415A8B	CLC426AIB	CLC502A8D	CNTR_BCD_SU_D
CLC415A8D	CLC426AJE	CLC502AID	CNTR_BIN_DEC_SU_D
CLC415AJE	CLC426AJP	CLC502AJE	CNTR_JOHNSON
CLC415AJP	CLC428A8B	CLC502AJP	CNY17F-3
CLC416AJE	CLC428AJE	CLC505A8D	CNY17F-3X001
CLC416AJP	CLC428AJP	CLC505AJE	CNY17F-3X006
CLC417AJE	CLC430A8B	CLC505AJP	CNY17F-3X007T
CLC417AJP	CLC430AJE	CLOCK_CURRENT	CNY17F-3X009T
CLC420A8B	CLC430AJP	CLOCK_VOLTAGE	CNY17F-3X016
CLC420A8D	CLC431A8B	CM1213A-02SR	CNY17F-3X017
CLC420AIB	CLC431AJE	CM1624-08DE	CNY17F-3X019
CLC420AJE	CLC431AJP	CNTR_16SBIN	COMP_4
CLC420AJP	CLC432A8B	CNTR_4ABIN	COMPARATOR_IDEAL
CLC420B8B	CLC432AJE	CNTR_4ADEC	

# Multisim 14.0 Education Components

---

COMPARATOR_VIRTUAL	COUNT_OFF_UPDOWN	CPH6445-TL-E	D44VH10G
COMPARHYS	COUNT_ON	CPH6531-TL-E	D45C12G
CONTROL_1A	COUNT_ON	CPM	D45H11G
CONTROL_1C	COUNT_ON_HOLD	CRYSTAL_VIRTUAL	D45H8G
CONTROL_2A	COUNT_ON_HOLD	CURRENT_CONTROLLED_CURRENT_SOURCE	D45VH10G
CONTROL_2C	COUNT_ON_RESET	CURRENT_CONTROLLED_SPST	DAC7642_FP32
CONTROL_3A	COUNT_ON_RESET	CURRENT_CONTROLLED_SPST_ANIMATED	DAC7643_FP32
CONTROL_3C	COUNT_ON_UPDOWN	CURRENT_CONTROLLED_VOLTAGE_SOURCE	DAC8541
CONTROL_4A	COUNT_UPDOWN_OFF	CURRENT_LIMITER_BLOCK	DAN222M3T5G
CONTROL_NC	COUNT_UPDOWN_ON	CYPRESS-ULTRA-ISR-HDR	DAP222M3T5G
CONTROL_NO	Counter_74LS160N	D_FF	DBREAK
CONTROLLED_ONE_SHOT	COUPLED_INDUCTORS	D_FF_NEGSR	DC_CURRENT
CONVEYOR_BELT	CPH3105-TL-E	D_FF_POSSR	DC_INTERACTIVE_CURRENT
CORELESS_COIL_VIRTUAL	CPH3123-TL-E	D_LATCH	DC_INTERACTIVE_VOLTAGE
CORESAT	CPH3144-TL-E	D_LATCH_NEGSR	DC_MACHINE_PERMANENT_MAGNET
COUNT_OFF	CPH3205-TL-E	D1N4148	DC_MACHINE_WOUND_FIELD
COUNT_OFF	CPH3223-TL-E	D44C12G	DC_POWER
COUNT_OFF_HOLD	CPH3448-TL-H	D44H11G	DC_XFMR
COUNT_OFF_HOLD	CPH5505-TL-E	D44H8G	DCC010-TB-E
COUNT_OFF_RESET	CPH5506-TL-E		DCD_2TO4
COUNT_OFF_RESET	CPH6223-TL-E		DCD_3TO8
	CPH6341-TL-E		DCD_4TO16



# Multisim 14.0 Education Components

---

DCD_7SEG	DF10SA-E3/45	DIP18	DPST_2NO_SB
DCD_7SEG_P	DF1510S-E3/77	DIP20	DQ_TO_ABC
DCD_BARGRAPH	DF3A6.8FUT1G	DIP22	DRV103H
DCD_HEX	DF6A6.8FUT1G	DIP24	DRV103U
DCD_HEX_BLUE	DGND	DIP28	DRV104PWP
DCD_HEX_DIG_BLU E	DIGITAL_CLOCK	DIP4	DRV8832DGQ
DCD_HEX_DIG_GRE EN	DIGITAL_CONSTAN T	DIP6	DRV8832DRCR
DCD_HEX_DIG_ORA NGE	DIGITAL_FREQUEN CY_DIVIDER	DIP8	DSUB15F
DCD_HEX_DIG_RED	DIGITAL_HIGH	DIPSW1	DSUB15F-VGA
DCD_HEX_DIG_YEL LOW	DIGITAL_LOW	DIPSW10	DSUB15M
DCD_HEX_GREEN	DIGITAL_PULLDOW N	DIPSW2	DSUB15M-VGA
DCD_HEX_ORANGE	DIGITAL_PULLUP	DIPSW3	DSUB25F
DCD_HEX_YELLOW	DIGITAL_STATE_MA CHINE	DIPSW4	DSUB25M
DEC_BCD_10_INV	DIODE	DIPSW5	DSUB37F
DEC_BCD_7	DIODE	DIPSW6	DSUB37M
DEC2_4	DIODE_RATED	DIPSW7	DSUB9F
DEC3_8	DIODE_THERMAL	DIPSW8	DSUB9M
DEC4_10	Diode1	DIPSW9	DSWPK_10
DELAY	DIP10	DIV	DSWPK_2
DEM4_16	DIP12	DIVIDER	DSWPK_3
DF06MA-E3/45	DIP14	DPDT_DB	DSWPK_4
DF10S/45	DIP16	DPDT_SB	DSWPK_5
		DPST_2NC_DB	DSWPK_6
		DPST_2NC_SB	DSWPK_7
		DPST_2NO_DB	DSWPK_8

# Multisim 14.0 Education Components

---

DSWPK_9	DTA144TET1G	DTC143EM3T5G	EDR201A05
DTA113EET1G	DTA144TM3T5G	DTC143TM3T5G	EDR201A12
DTA113EM3T5G	DTA144WM3T5G	DTC143ZET1G	EDR201A24
DTA114EET1G	DTAND	DTC143ZM3T5G	EDR2H1A05
DTA114EM3T5G	DTC113EET1G	DTC144EET1G	EDR2H1A12
DTA114TET1G	DTC113EM3T5G	DTC144EM3T5G	EDR2H1A24
DTA114TM3T5G	DTC114EET1G	DTC144TET1G	EGF1D-E3/67A
DTA114YET1G	DTC114EM3T5G	DTC144TM3T5G	EGF1T-E3/67A
DTA114YM3T5G	DTC114TET1G	DTC144WM3T5G	EGP10D-E3/54
DTA115EET1G	DTC114TM3T5G	DTMF_KEYPAD	EGP10G-E3/54
DTA115EM3T5G	DTC114YET1G	ECG6407	EGP50D-E3/54
DTA115TET1G	DTC115EET1G	ECG6408	EGP50G-E3/54
DTA115TM3T5G	DTC115EM3T5G	ECG6411	EL2006CG
DTA123EM3T5G	DTC115TET1G	ECG6412	EL2006G
DTA123TET1G	DTC115TM3T5G	ECH8102-TL-H	EL2006G/883B
DTA123TM3T5G	DTC123EM3T5G	ECH8649-TL-H	EL2022/EL
DTA124EET1G	DTC123JET1G	ECH8651R-R-TL-H	EL2022CG
DTA124EM3T5G	DTC123JM3T5G	ECH8651R-TL-H	EL2022G
DTA124XM3T5G	DTC123TET1G	ECH8652-TL-H	EL2157CN
DTA143EET1G	DTC123TM3T5G	ECH8653-TL-H	EL2157CS
DTA143EM3T5G	DTC124EET1G	ECH8654-TL-H	EL2210CN
DTA143ZET1G	DTC124EM3T5G	ECH8657-TL-H	EL2210CS
DTA143ZM3T5G	DTC124XET1G	ECH8660-TL-H	EL2211CN
DTA144EET1G	DTC124XM3T5G	ECH8662-TL-H	EL2211CS
DTA144EM3T5G	DTC143EET1G	EDF1DS-E3/45	EL2310CN

# Multisim 14.0 Education Components

---

EL2310CS	Elvis_II_Rail_Right_Bottom	EMR011A03	EMR021B09
EL2311CN		EMR011A05	EMR021B12
EL2311CS	Elvis_II_Rail_Right_Top	EMR011A06	EMR021B24
EL2410CN	Elvis_II_top_fixed_1	EMR011A08	EMR031A03
EL2410CS	Elvis_II_top_fixed_2	EMR011A09	EMR031A05
EL2411CN	Elvis_Left_Rail1	EMR011A12	EMR031A06
EL2411CS	Elvis_Left_Rail2	EMR011A24	EMR031A08
EL2500/EL	Elvis_Left_Rail3	EMR011B03	EMR031A09
EL2520/EL	Elvis_Left_Rail4	EMR011B05	EMR031A12
EL2600/EL	Elvis_Left_Rail5	EMR011B06	EMR031A24
EL2620/EL	Elvis_Left_Rail6	EMR011B08	EMR031B03
EL4089CN	Elvis_Left_Rail7	EMR011B09	EMR031B05
EL4089CS	Elvis_Left_Rail8	EMR011B12	EMR031B06
EL4430CN	Elvis_Left_Rail9	EMR011B24	EMR031B08
EL4430CS	Elvis_Right_Rail	EMR021A03	EMR031B09
EL4451CN	ElvisLbIA	EMR021A05	EMR031B12
EL4451CS	ElvisLbIB	EMR021A06	EMR031B24
EL4452CN	ElvisResistor	EMR021A08	EMR121A03
EL4452CS	EMC2DXV5T1G	EMR021A09	EMR121A05
ELH0032G/883B	EMC3DXV5T1G	EMR021A12	EMR121A06
ELH0101K/883B	EMC3DXV5T5G	EMR021A24	EMR121A08
Elvis_II_Rail_left_Bottom	EMC4DXV5T1G	EMR021B03	EMR121A09
	EMC5DXV5T1G	EMR021B05	EMR121A12
Elvis_II_Rail_Left_Top	EMH1303-TL-E	EMR021B06	EMR121A24
	EMH1405-TL-H	EMR021B08	EMR121B03

# Multisim 14.0 Education Components

---

EMR121B05	EMR151A12	ENERGIZING_COIL_ AC	EPC8002
EMR121B06	EMR151A24		EPC8003
EMR121B08	EMR161A03	ENERGIZING_COIL_ TIMED	EPC8004
EMR121B09	EMR161A05	EP2015ACN	EPC8005
EMR121B12	EMR161A06	EP2015CM	EPC8007
EMR121B24	EMR161A08	EP2015CN	EPC8008
EMR131A03	EMR161A09	EPC2001	EPC8009
EMR131A05	EMR161A12	EPC2007	EPC8010
EMR131A06	EMR171A03	EPC2010	ERRAMP
EMR131A08	EMR171A05	EPC2012	ES1B-E3/61T
EMR131A09	EMR171A06	EPC2014	ES1C-E3/61T
EMR131A12	EMR171A08	EPC2015	ES1D-E3/61T
EMR131A24	EMR171A09	EPC2016	ES1PD-E3/84A
EMR131B03	EMR171A12	EPC2018	ES2B-E3/52T
EMR131B05	EMR171A24	EPC2019	ES2C-E3/52T
EMR131B06	EMX1DXV6T1G	EPC2020	ES2D-E3/52T
EMR131B08	EMX1DXV6T5G	EPC2021	ES3D-E3/57T
EMR131B09	EN2016CM	EPC2022	ESD0P2RF-02LRH
EMR131B12	EN2016CN	EPC2023	ESD0P2RF-02LS
EMR131B24	ENC_10TO4	EPC2024	ESD11L5.0DT5G
EMR151A03	ENC_8TO3	EPC2025	ESD18VU1B-02LRH
EMR151A05	ENC_8TO3S	EPC2100	ESD18VU1B-02LS
EMR151A06	ENC10_4	EPC2801	ESD3V3U4ULC
EMR151A08	ENC8_3	EPC2815	ESD5B5.0ST1G
EMR151A09	ENERGIZING_COIL	EPC2818	ESD5V3L1B-02LS

# Multisim 14.0 Education Components

---

ESD5V3U4U-HDMI	ESD9X3.3ST5G	F1240	FES16GT-E3/45
ESD5Z12T1G	ESD9X5.0ST5G	F1260	FES8DT-E3/45
ESD5Z2.5T1G	ESDR0502NMUTAG	F2001	FF_D_CO
ESD5Z3.3T1G	ESDR0502NMUTBG	F2002	FF_D_PCLR_CO
ESD5Z5.0T1G	ESDR0544MDMR4G	F2012	FF_D4_CLR_CO
ESD5Z6.0T1G	ESH1PD-E3/84A	F2021	FF_JK_NSCLR_CO
ESD5Z7.0T1G	EVAL-SDP-CB1Z	F2046	FF_JK_PSCLR_CO
ESD5Z7.0T5G	EVAL-SDP-CH1Z	F2047	FF_T_CLR_CO
ESD7004MUTAG	EVAL-SDP-CH1Z_FMC	F2048	FF200R12KE4
ESD7008MUTAG	EVAL-SDP-CS1Z	F2201S	FF300R12KE4
ESD7016MUTAG	EXPONENTIAL_CURRENT	F2202S	FF450R12KE4
ESD7104MUTAG	EXPONENTIAL_VOLTAGE	FAST_1A	FLOAT_NC
ESD7951ST5G		FAST_2A	FLOAT_NO
ESD7C3.3DT5G		FAST_3A	FLOW_NC
ESD7C5.0DT5G	F1007	FAST_4A	FLOW_NO
ESD8004MUTAG	F1008	FCN-268D024-G/10-R	FLYBACKCCM
ESD8040MUTAG	F1020	FCX458	FLYBACKCM
ESD8V0R1B-02EL	F1021	FCX558	FLYBACKDCM
ESD8V0R1B-02ELS	F1022	FCX649	FLYBACKVM
ESD9B3.3ST5G	F1027	FCX749	FM_CURRENT
ESD9B5.0ST5G	F1072	FEP16DT-E3/45	FM_VOLTAGE
ESD9C3.3ST5G	F1074	FEP30GP-E3/45	FMMD2835
ESD9C5.0ST5G	F1120	FEP30JPE3/45	FMMD2836
ESD9L5.0ST5G	F1174	FES16BT-E3/45	FMMD2837
ESD9X12ST5G	F1214		FMMD2838

# Multisim 14.0 Education Components

---

FMMD6050	FMMTA20	FS50R12W2T4	FZT604
FMMD6100	FMMTA70	FS75R12W2T4	FZT605
FMMD7000	FMMTH10	FSK_VOLTAGE	FZT649
FMMD914	FMMV105G	FULL_ADDER	FZT651
FMMT38B	FMMV109	FULL_CM	FZT653
FMMT489	FMMV2101	FULL_VM	FZT657
FMMT491A	FMMV2102	FUSE	FZT658
FMMT497	FMMV2103	FUSE_RATED	FZT688B
FMMT5179	FMMV2104	FUSE_VIRTUAL	FZT689B
FMMT549	FMMV2105	FWDCCM	FZT690B
FMMT589	FMMV2106	FWDDCM	FZT692B
FMMT591A	FMMV2107	FX2-100S- 1.27DS(71)	FZT694B
FMMT597	FMMV2108	FX8-120P-SV1(91)	FZT696B
FMMT597Q	FMMV2109	FX8-120S-SV(21)	FZT705
FMMT617	FMMV3102	FZ600R12KE4	FZT749
FMMT618	FOOT_NC	FZ900R12KP4	FZT751
FMMT619	FOOT_NO	FZT1047A	FZT753
FMMT624	FORWARDCM	FZT1048A	FZT757
FMMT625	FORWARDVM	FZT1049A	FZT758
FMMT717	FREQ_DIVIDER	FZT1051A	FZT788A
FMMT718	FREQUENCY_TABLE _FUNCTION	FZT1053A	FZT788B
FMMT720	FS100R12KT4	FZT1147A	FZT789A
FMMT722	FS150R12KT4	FZT1149A	FZT790A
FMMT723	FS25R12W1T4	FZT1151A	FZT792A
FMMT918			FZT795A

# Multisim 14.0 Education Components

---

FZT796A	GF1A	GL34J	GLL4759
FZT849	GF1B	GLL4735	GLL4760
FZT851	GF1D	GLL4736	GLL4761
FZT857	GF1G	GLL4737	GLL4762
FZT869	GF1G-E3/67A	GLL4738	GLL4763
FZT948	GF1J	GLL4739	GP02-20
FZT949	GF1K	GLL4740	GP02-25
FZT951	GF1M	GLL4741	GP02-30
FZT953	GI250-1	GLL4742	GP02-35
FZT955	GI250-2	GLL4743	GP02-40
FZT956	GI250-3	GLL4744	GP08A
FZT957	GI250-4	GLL4745	GP08B
FZT958	GI751-E3/54	GLL4746	GP08D
FZT968	GI810	GLL4747	GP08G
G3SBA60-E3/51	GI811	GLL4748	GP08J
GaAsFET_N	GI812	GLL4749	GP10A
GaAsFET_P	GI814	GLL4750	GP10B
GAIN_2_PIN	GI816	GLL4751	GP10D
GBPC3506W-E4/51	GI817	GLL4752	GP10G
GBU4G-E3/45	GI818	GLL4753	GP10J
GBU4M-E3/51	GL34A	GLL4754	GP10K
GBU6G-E3/45	GL34B	GLL4755	GP10M
GBU6M-E3/45	GL34D	GLL4756	GP10N
GEARS	GL34G	GLL4757	GP10Q
GEN_CNTR_4ABIN	GL34G-E3/98	GLL4758	GP10T

# Multisim 14.0 Education Components

---

GP10V	GRAPH_LCD_S	HA1-4741-2	HA2-2548-9
GP10W	GROUND	HA1-4741-5	HA2-2600-2
GP10Y	GROUND_REF1	HA1-5104-2	HA2-2602-2
GP10Y-E3/54	GROUND_REF2	HA1-5104-5	HA2-2605-5
GP15A	GROUND_REF3	HA1-5114-2	HA2-2620-2
GP15B	GROUND_REF4	HA1-5114-5	HA2-2622-2
GP15D	GROUND_REF5	HA1-5134-2	HA2-2625-5
GP15G	GSB311A41EU	HA1-5134-5	HA2-2640-2
GP15J	GSB3211311WEU	HA1-5190-2	HA2-5101-2
GP15K	GSIB1580-E3/45	HA2-2500-2	HA2-5102-2
GP15M	GSIB2560-E3/45	HA2-2502-2	HA2-5102-5
GP20A	GTO	HA2-2510-2	HA2-5130-5
GP20B	HA1-2539-2	HA2-2512-2	HA2-5135-5
GP20D	HA1-2539-5	HA2-2515-2	HA2-5142-2
GP20G	HA1-2540-2	HA2-2520-2	HA2-5142-5
GP20J	HA1-2540-5	HA2-2522-2	HA2-5147-2
GP30A	HA1-2541-2	HA2-2525-5	HA2-5147-5
GP30B	HA1-2541-5	HA2-2529-2	HA2-5160-2
GP30D	HA1-2542-2	HA2-2529-5	HA2-5160-5
GP30G	HA1-2542-5	HA2-2541-2	HA2-5162-5
GP30J	HA1-2839-5	HA2-2541-5	HA2-5170-2
GP30K	HA1-2840-5	HA2-2542-2	HA2-5170-5
GP30M	HA1-2840-9	HA2-2542-5	HA2-5190-2
GRAPH_LCD_L	HA1-2850-5	HA2-2544-2	HA2-5221-5
GRAPH_LCD_M	HA1-2850-9	HA2-2548-5	HA2-7712A-5



# Multisim 14.0 Education Components

---

HA2-7712A-9	HA3-2850-9	HA3B2842-5	HA7-2840-9
HA2-7712B-5	HA3-4741-5	HA3B2842-9	HA7-2850-5
HA2-7712B-9	HA3-5101-5	HA3B2850-5	HA7-2850-9
HA3-2444-5	HA3-5102-5	HA3B2850-9	HA7-5101-2
HA3-2444-9	HA3-5104-5	HA4P2525-5	HA7-5102-2
HA3-2525-5	HA3-5111-5	HA7-2500-2	HA7-5102-5
HA3-2529-5	HA3-5112-5	HA7-2510-2	HA7-5111-2
HA3-2539-5	HA3-5114-5	HA7-2512-2	HA7-5112-2
HA3-2539C-5	HA3-5127-5	HA7-2515-2	HA7-5127-2
HA3-2540-5	HA3-5127A-5	HA7-2520-2	HA7-5127-5
HA3-2542-5	HA3-5142-5	HA7-2522-2	HA7-5127A-2
HA3-2544-5	HA3-5147-5	HA7-2525-5	HA7-5127A-5
HA3-2544C-5	HA3-5177-5	HA7-2529-5	HA7-5130-2
HA3-2548-5	HA3-5221-5	HA7-2544-2	HA7-5130-5
HA3-2605-5	HA3-5222-5	HA7-2544-5	HA7-5135-2
HA3-2625-5	HA3-5232-5	HA7-2548-5	HA7-5135-5
HA3-2839-5	HA3-5232-9	HA7-2600-2	HA7-5137-2
HA3-2839-9	HA3-7712A-5	HA7-2602-2	HA7-5137-5
HA3-2840-5	HA3-7712A-9	HA7-2605-5	HA7-5142-2
HA3-2840-9	HA3-7712B-5	HA7-2620-2	HA7-5142-5
HA3-2841-5	HA3-7712B-9	HA7-2622-2	HA7-5147-2
HA3-2841-9	HA3B2840-5	HA7-2625-5	HA7-5147-5
HA3-2842-5	HA3B2840-9	HA7-2640-2	HA7-5170-2
HA3-2842-9	HA3B2841-5	HA7-2645-5	HA7-5170-5
HA3-2850-5	HA3B2841-9	HA7-2840-5	HA7-5177-5

# Multisim 14.0 Education Components

---

HA7-5221-5	HA9P4741-9	HALF_VM	HCNW139-300E
HA7-5221-9	HA9P5101-5	HC-49/U_1.5MHz	HCNW2201-000E
HA7-5222-5	HA9P5101-9	HC-49/U_11MHz	HCNW2201-300E
HA7-5222-9	HA9P5102-5	HC-49/U_15MHz	HCNW3120-000E
HA9P2444-5	HA9P5102-9	HC-49/U_25MHz	HCNW3120-300E
HA9P2444-9	HA9P5104-5	HC-49/U_3MHz	HCPL-0201-000E
HA9P2529-5	HA9P5104-9	HC-49/U_40MHz	HCPL-0201-060E
HA9P2539-5	HA9P5111-5	HC-49/U_5MHz	HCPL-0211-000E
HA9P2539-9	HA9P5111-9	HC-49/U_7MHz	HCPL-0211-060E
HA9P2540-5	HA9P5112-5	HC-49/U_80MHz	HCPL-0302-000E
HA9P2544-5	HA9P5112-9	HC-49/US_11MHz	HCPL-0302-060E
HA9P2544-9	HA9P5114-5	HC-49/US_15MHz	HCPL-0314-000E
HA9P2544C-5	HA9P5114-9	HC-49/US_25MHz	HCPL-0314-060E
HA9P2544C-9	HA9P5127-5	HC-49/US_40MHz	HCPL-0454-000E
HA9P2548-5	HA9P5137-5	HC-49/US_5MHz	HCPL-0454-060E
HA9P2605-5	HA9P5142-9	HC-49/US_7MHz	HCPL-0466-000E
HA9P2625-5	HA9P5221-5	HCNR200	HCPL-0466-060E
HA9P2840-5	HA9P5222-5	HCNR200-000E	HCPL-0501-500E
HA9P2840-9	HA9P5222-9	HCNR200-050E	HCPL-0501-560E
HA9P2841-5	HA9P5232-5	HCNR200-300E	HCPL0631
HA9P2841-9	HA9P5232-9	HCNR200-350E	HCPL-063L-000E
HA9P2842-5	HA9P7712B-5	HCNR201	HCPL-063L-060E
HA9P2842-9	HA9P7712B-9	HCNW136-000E	HCPL-0701-000E
HA9P2850-5	HALF_ADDER	HCNW136-300E	HCPL-0701-060E
HA9P2850-9	HALF_CM	HCNW139-000E	HCPL-181-000E

# Multisim 14.0 Education Components

---

HCPL-181-060E	HCPL-2232-000E	HCPL-4504-360E	HDR1X22
HCPL-2200-000E	HCPL-2232-300E	HCPL-4506-000E	HDR1X23
HCPL-2200-300E	HCPL-263L-000E	HCPL-4506-020E	HDR1X24
HCPL-2201-000E	HCPL-263L-020E	HCPL-4506-060E	HDR1X25
HCPL-2201-060E	HCPL-263L-060E	HCPL-4506-300E	HDR1X3
HCPL-2201-300E	HCPL-263L-300E	HCPL-4506-320E	HDR1X4
HCPL-2201-360E	HCPL-263L-320E	HCPL-4506-360E	HDR1X5
HCPL-2202-000E	HCPL-263L-560E	HCPL-7800-000E	HDR1X6
HCPL-2202-060E	HCPL-3020-000E	HCPL-7800-300E	HDR1X7
HCPL-2202-300E	HCPL-3020-060E	HCPL-J312-000E	HDR1X8
HCPL-2202-360E	HCPL-3020-300E	HCPL-J312-300E	HDR1X9
HCPL-2211-000E	HCPL-3120-000E	HD4A	HDR2X10
HCPL-2211-060E	HCPL-3120-060E	HDR1X10	HDR2X11
HCPL-2211-300E	HCPL-3120-300E	HDR1X11	HDR2X12
HCPL-2211-360E	HCPL-3120-360E	HDR1X12	HDR2X13
HCPL-2212-000E	HCPL-3140-000E	HDR1X13	HDR2X14
HCPL-2212-060E	HCPL-3140-060E	HDR1X14	HDR2X15
HCPL-2212-300E	HCPL-3140-300E	HDR1X15	HDR2X16
HCPL-2212-360E	HCPL-3140-360E	HDR1X16	HDR2X17
HCPL-2219-000E	HCPL-316J-000E	HDR1X17	HDR2X18
HCPL-2219-060E	HCPL-4504-000E	HDR1X18	HDR2X19
HCPL-2219-300E	HCPL-4504-020E	HDR1X19	HDR2X2
HCPL-2219-360E	HCPL-4504-060E	HDR1X2	HDR2X20
HCPL-2231-000E	HCPL-4504-300E	HDR1X20	HDR2X21
HCPL-2231-300E	HCPL-4504-320E	HDR1X21	HDR2X22

# Multisim 14.0 Education Components

---

HDR2X23	HEL-775-AT0	HFA08TB60	HFA9P0002-9
HDR2X24	HEL-775-AU0	HFA1-0001-5	HFA9P0005-5
HDR2X25	HEL-775-BT0	HFA1-0001-9	HFA9P0005-9
HDR2X3	HEL-775-BU0	HFA15TB60	HFB16HY20C
HDR2X4	HEL-776-AT0	HFA16PB120	HFB20HJ20C
HDR2X5	HEL-776-AU0	HFA2-0002-5	HFB25HJ20
HDR2X6	HEL-777-AT0	HFA2-0002-9	HFB35HB20
HDR2X7	HEL-777-AU0	HFA2-0005-5	HFB35HB20C
HDR2X8	HELD_CLOSED_LIMIT	HFA2-0005-9	HFB50HC20
HDR2X9		HFA25TB60	HFB50HC20C
HEL-700-T0A	HELD_OPEN_LIMIT	HFA3-0001-5	HFB50HI20
HEL-700-T0B	HF30ACC201209	HFA3-0001-9	HFB50HI20C
HEL-700-U0A	HF30ACC321611	HFA3-0002-5	HFB60HF20
HEL-700-U0B	HF30ACC322513	HFA3-0002-9	HFB60HF20C
HEL-700-U0C	HF30ACC453215	HFA3-0005-5	HM1-65642-883
HEL-705-U012	HF50ACC201209	HFA3-0005-9	HM1-65642B-883
HEL-707-U012	HF50ACC321611	HFA30PA60C	HM1-65642C-883
HEL-711-T012	HF50ACC322513	HFA35HB120	HM4-65642-883
HEL-711-U012	HF50ACC453215	HFA45HC60C	HM4-65642B-883
HEL-712-T012	HF70ACC201209	HFA7-0002-5	HM6116A120
HEL-712-U012	HF70ACC321611	HFA7-0002-9	HOLDING_TANK
HEL-716-T012	HF70ACC322513	HFA7-0005-5	HRTS-5760-BU012
HEL-716-U012	HF70ACC453215	HFA7-0005-9	HRTS-61-T024
HEL-717-T012	HFA04TB60	HFA9P0001-5	HRTS-61-U024
HEL-717-U012	HFA08PB120	HFA9P0002-5	HSDL-5400

# Multisim 14.0 Education Components

---

HSDL-5420	ICM7555MJA	IDD09E60	IDH10G65C5
HSDL-5420#031	ICM7555MTV	IDD09SG60C	IDH10S120
ICL7611ACPA	ICM7556IPD+	IDD10SG60C	IDH10S60C
ICL7611ACTV	ICM7556ISD+	IDD12SG60C	IDH10SG60C
ICL7611AMTV	ICM7556MJD+	IDD15E60	IDH12G65C5
ICL7611DCBA	IDAC	IDD23E60	IDH12S60C
ICL7650SCBA-1	IDAC16	IDH02G65C5	IDH15S120
ICL7650SCBD	IDB04E120	IDH02SG120	IDH16G65C5
ICL7650SCPA	IDB06E60	IDH03G65C5	IDH16S60C
ICL7650SCPD	IDB09E120	IDH04G65C5	IDH20G65C5
ICL7650SCTV-1	IDB09E60	IDH04S60C	IDL02G65C5
ICL7650SIJD	IDB12E120	IDH04SG60C	IDL04G65C5
ICL7650SIPA-1	IDB15E60	IDH05G65C5	IDL06G65C5
ICL7650SIPD	IDB18E120	IDH05S120	IDL08G65C5
ICL7650SITV-1	IDB23E60	IDH05S60C	IDL10G65C5
ICL7650SMJD	IDB30E120	IDH05SG60C	IDL12G65C5
ICL7650SMTV-1	IDB30E60	IDH06G65C5	IDP04E120
ICL7652	IDB45E60	IDH06S60C	IDP06E60
ICL7652D	IDD03E60	IDH06SG60C	IDP09E120
ICL7652P	IDD03SG60C	IDH08G65C5	IDP09E60
ICM7555ESA+	IDD04SG60C	IDH08S120	IDP12E120
ICM7555IJA+	IDD05SG60C	IDH08S60C	IDP15E60
ICM7555IPA+	IDD06E60	IDH08SG60C	IDP18E120
ICM7555ISA+	IDD06SG60C	IDH09G65C5	IDP23E60
ICM7555ITV	IDD08SG60C	IDH09SG60C	IDP30E120

# Multisim 14.0 Education Components

---

IDP30E60	INA148UA	INA2126EA/250	INA321EA
IDP45E60	INA152EA/250	INA2126P	INA322EA
IDW10G65C5	INA154U	INA2126U	INA326EA
IDW10S120	INA154UA	INA212AIDCKR	INA327EA
IDW12G65C5	INA157U	INA212BIDCKR	INA331AIDGK
IDW15S120	INA157UA	INA2132U	INA331IDGK
IDW16G65C5	INA159AID	INA2132UA	INA332IDGK
IDW20G65C5	INA163UA	INA213AIDCKR	INA333AIDGKR
IDW20S120	INA168NA	INA213AIDCKT	INA333AIDRGR
IDW30G65C5	INA169NA	INA213AIRSWR	INCREMENTAL_ENC ODER
IDW30S120	INA170EA	INA213BIDCKR	INDICATOR
IDW40G65C5	INA193AID	INA213BIRSWR	INDUCTION_MACHI NE_SQUIRREL_CAG E
IGBT_DIODE_THER MAL	INA194AID	INA214AIDCKR	
	INA195AID	INA214AIRSWR	
IJW120R070T1	INA201AID	INA214BIDCKR	INDUCTION_MACHI NE_SQUIRREL_CAG E_E
IJW120R100T1	INA201AIDGKR	INA214BIRSWR	
ILLUMINATED_PB	INA206AID	INA216A2RSWR	INDUCTION_MACHI NE_WOUND
INA105_CMP	INA206AIPW	INA216A2YFFR	
INA133U	INA210AIDCKR	INA216A3RSWR	INDUCTION_MACHI NE_WOUND_E
INA133UA	INA210AIRSWR	INA216A3YFFR	
INA138NA	INA210BIDCKR	INA216A4RSWR	INDUCTOR_COUPLI NG
INA143U	INA210BIRSWR	INA216A4YFFR	Inductor_Lossy
INA143UA	INA211AIDCKR	INA270AID	INDUCTOR_RATED
INA145UA	INA211BIDCKR	INA271AID	INDUCTOR_VIRTUA L
INA146UA	INA2126E/250	INA321E	

# Multisim 14.0 Education Components

---

Inductor1_1.0uH	IPA057N06N3 G	IPA60R125CP	IPA65R190E6
Inductor2_1.0uH	IPA057N08N3 G	IPA60R160C6	IPA65R225C7
INERTIAL_LOAD	IPA075N15N3 G	IPA60R165CP	IPA65R280C6
INPUT_CONTACT_N C	IPA086N10N3 G	IPA60R190C6	IPA65R280E6
INPUT_CONTACT_N O	IPA093N06N3 G	IPA60R190E6	IPA65R310CFD
INPUT_MODULE_1 20Vdc	IPA100N08N3 G	IPA60R199CP	IPA65R380C6
INPUT_MODULE_1 2Vdc	IPA105N15N3 G	IPA60R250CP	IPA65R380E6
INPUT_MODULE_1 2Vdc	IPA126N10N3 G	IPA60R280C6	IPA65R420CFD
INPUT_MODULE_2 40Vdc	IPA180N10N3 G	IPA60R280E6	IPA65R600C6
INPUT_MODULE_2 40Vdc	IPA50R140CP	IPA60R299CP	IPA65R600E6
INPUT_MODULE_2 4Vdc	IPA50R190CE	IPA60R380C6	IPA65R660CFD
INPUT_MODULE_2 4Vdc	IPA50R199CP	IPA60R380E6	IPA90R1K0C3
INPUT_MODULE_3 0Vdc	IPA50R250CP	IPA60R385CP	IPA90R1K2C3
INPUT_MODULE_3 0Vdc	IPA50R280CE	IPA60R520C6	IPA90R340C3
INPUT_MODULE_5 Vdc	IPA50R299CP	IPA60R520E6	IPA90R500C3
INPUT_MODULE_5 Vdc	IPA50R350CP	IPA60R600C6	IPA90R800C3
INPUT_MODULE_9 Vdc	IPA50R380CE	IPA60R600E6	IPB009N03L G
INPUT_MODULE_9 Vdc	IPA50R399CP	IPA60R950C6	IPB010N06N
INTERACTIVE_DIGIT AL_CONSTANT	IPA50R500CE	IPA65R045C7	IPB011N04L G
INV	IPA50R520CP	IPA65R065C7	IPB011N04N G
IPA028N08N3 G	IPA50R650CE	IPA65R095C7	IPB014N06N
IPA030N10N3 G	IPA50R800CE	IPA65R125C7	IPB015N04L G
IPA032N06N3 G	IPA50R950CE	IPA65R190C6	IPB015N04N G
IPA037N08N3 G	IPA60R099C6	IPA65R190C7	IPB016N06L3 G
IPA045N10N3 G	IPA60R125C6	IPA65R190CFD	IPB017N06N3 G

# Multisim 14.0 Education Components

---

IPB019N06L3 G	IPB042N03L G	IPB108N15N3 G	IPB60R385CP
IPB019N08N3 G	IPB042N10N3 G	IPB114N03L G	IPB65R045C7
IPB020N04N G	IPB048N06L G	IPB123N10N3 G	IPB65R065C7
IPB020NE7N3 G	IPB049N06L3 G	IPB136N08N3 G	IPB65R095C7
IPB021N06N3 G	IPB049NE7N3 G	IPB144N12N3 G	IPB65R110CFDA
IPB022N04L G	IPB050N06N G	IPB147N03L G	IPB65R125C7
IPB023N04N G	IPB052N04N G	IPB200N15N3 G	IPB65R150CFDA
IPB023N06N3 G	IPB054N06N3 G	IPB200N25N3 G	IPB65R190C7
IPB025N08N3 G	IPB054N08N3 G	IPB230N06L3 G	IPB65R190CFD
IPB025N10N3 G	IPB055N03L G	IPB260N06N3 G	IPB65R190CFDA
IPB026N06N	IPB057N06N	IPB26CN10N G	IPB65R225C7
IPB027N10N3 G	IPB065N03L G	IPB320N20N3 G	IPB65R310CFDA
IPB029N06N3 G	IPB065N15N3 G	IPB34CN10N G	IPB65R660CFD
IPB030N08N3 G	IPB067N08N3 G	IPB50CN10N G	IPB65R660CFDA
IPB031NE7N3 G	IPB072N15N3 G	IPB50R140CP	IPD025N06N
IPB034N03L G	IPB075N04L G	IPB50R199CP	IPD031N03L G
IPB034N06L3 G	IPB080N03L G	IPB50R250CP	IPD031N06L3 G
IPB034N06N3 G	IPB081N06L3 G	IPB50R299CP	IPD034N06N3 G
IPB035N08N3 G	IPB083N10N3 G	IPB530N15N3 G	IPD035N06L3 G
IPB036N12N3 G	IPB090N06N3 G	IPB600N25N3 G	IPD036N04L G
IPB037N06N3 G	IPB093N04L G	IPB60R099CP	IPD038N04N G
IPB038N12N3 G	IPB096N03L G	IPB60R125CP	IPD038N06N3 G
IPB039N04L G	IPB097N08N3 G	IPB60R165CP	IPD040N03L G
IPB039N10N3 G	IPB107N20N3 G	IPB60R199CP	IPD042P03L3 G
IPB041N04N G	IPB107N20NA	IPB60R250CP	IPD048N06L3 G



# Multisim 14.0 Education Components

---

IPD050N03L G	IPD180N10N3 G	IPD60R380C6	IPI034NE7N3 G
IPD053N06N	IPD200N15N3 G	IPD60R520C6	IPI037N06L3 G
IPD053N06N3 G	IPD220N06L3 G	IPD60R600C6	IPI037N08N3 G
IPD053N08N3 G	IPD230N06N G	IPD60R600E6	IPI040N06N3 G
IPD060N03L G	IPD250N06N3 G	IPD60R950C6	IPI041N12N3 G
IPD068N10N3 G	IPD25CN10N G	IPD640N06L G	IPI045N10N3 G
IPD068P03L3 G	IPD320N20N3 G	IPD65R190C7	IPI04CN10N G
IPD075N03L G	IPD33CN10N G	IPD65R225C7	IPI052NE7N3 G
IPD079N06L3 G	IPD350N06L G	IPD65R380C6	IPI057N08N3 G
IPD082N10N3 G	IPD400N06N G	IPD65R380E6	IPI070N08N3 G
IPD088N04L G	IPD50R1K4CE	IPD65R420CFD	IPI072N10N3 G
IPD088N06N3 G	IPD50R280CE	IPD65R420CFDA	IPI075N15N3 G
IPD090N03L G	IPD50R2K0CE	IPD65R600C6	IPI076N12N3 G
IPD096N08N3 G	IPD50R380CE	IPD65R600E6	IPI084N06L3 G
IPD105N03L G	IPD50R399CP	IPD65R660CFD	IPI086N10N3 G
IPD105N04L G	IPD50R3K0CE	IPD78CN10N G	IPI100N08N3 G
IPD110N12N3 G	IPD50R500CE	IPD800N06N G	IPI110N20N3 G
IPD122N10N3 G	IPD50R520CP	IPD90R1K2C3	IPI111N15N3 G
IPD127N06L G	IPD50R650CE	IPI020N06N	IPI126N10N3 G
IPD12CN10N G	IPD50R800CE	IPI023NE7N3 G	IPI139N08N3 G
IPD135N03L G	IPD50R950CE	IPI024N06N3 G	IPI147N12N3 G
IPD135N08N3 G	IPD530N15N3 G	IPI028N08N3 G	IPI180N10N3 G
IPD144N06N G	IPD600N25N3 G	IPI029N06N	IPI200N15N3 G
IPD160N04L G	IPD60R1K4C6	IPI030N10N3 G	IPI200N25N3 G
IPD170N04N G	IPD60R2K0C6	IPI032N06N3 G	IPI26CN10N G

# Multisim 14.0 Education Components

---

IPI320N20N3 G	IPP024N06N3 G	IPP062NE7N3 G	IPP147N12N3 G
IPI35CN10N G	IPP028N08N3 G	IPP065N03L G	IPP16CN10L G
IPI50CN10N G	IPP029N06N	IPP06CN10L G	IPP16CN10N G
IPI50R350CP	IPP030N10N3 G	IPP070N08N3 G	IPP180N10N3 G
IPI530N15N3 G	IPP032N06N3 G	IPP072N10N3 G	IPP200N15N3 G
IPI600N25N3 G	IPP034N03L G	IPP075N15N3 G	IPP200N25N3 G
IPI60R250CP	IPP034NE7N3 G	IPP076N12N3 G	IPP230N06L3 G
IPI80CN10N G	IPP037N06L3 G	IPP080N03L G	IPP260N06N3 G
IPI90R1K0C3	IPP037N08N3 G	IPP084N06L3 G	IPP26CN10N G
IPI90R1K2C3	IPP040N06N	IPP085N06L G	IPP320N20N3 G
IPI90R500C3	IPP040N06N3 G	IPP086N10N3 G	IPP50CN10N G
IPI90R800C3	IPP041N04N G	IPP08CN10L G	IPP50R140CP
IPL60R199CP	IPP041N12N3 G	IPP093N06N3 G	IPP50R190CE
IPL60R299CP	IPP042N03L G	IPP096N03L G	IPP50R199CP
IPL60R385CP	IPP045N10N3 G	IPP100N08N3 G	IPP50R250CP
IPL65R070C7	IPP048N12N3 G	IPP110N20N3 G	IPP50R280CE
IPL65R099C7	IPP04CN10N G	IPP110N20NA	IPP50R299CP
IPL65R130C7	IPP052N06L3 G	IPP111N15N3 G	IPP50R350CP
IPL65R195C7	IPP052NE7N3 G	IPP114N03L G	IPP50R380CE
IPL65R230C7	IPP055N03L G	IPP114N12N3 G	IPP50R399CP
IPP015N04N G	IPP057N06N3 G	IPP120N06N G	IPP50R500CE
IPP020N06N	IPP057N08N3 G	IPP126N10N3 G	IPP50R520CP
IPP023N04N	IPP05CN10L G	IPP12CN10L G	IPP530N15N3 G
IPP023N04N G	IPP05CN10N G	IPP139N08N3 G	IPP600N25N3 G
IPP023NE7N3 G	IPP060N06N	IPP147N03L G	IPP60R099C6

# Multisim 14.0 Education Components

---

IPP60R099CP	IPP65R110CFDA	IPP90R800C3	IPW60R041C6
IPP60R125C6	IPP65R125C7	IPS031N03L G	IPW60R045CP
IPP60R125CP	IPP65R150CFDA	IPS040N03L G	IPW60R070C6
IPP60R160C6	IPP65R190C6	IPS050N03L G	IPW60R075CP
IPP60R165CP	IPP65R190C7	IPS060N03L G	IPW60R099C6
IPP60R190C6	IPP65R190CFD	IPS075N03L G	IPW60R099CP
IPP60R190E6	IPP65R190CFDA	IPS090N03L G	IPW60R125C6
IPP60R199CP	IPP65R190E6	IPS105N03L G	IPW60R125CP
IPP60R1K4C6	IPP65R225C7	IPS110N12N3 G	IPW60R160C6
IPP60R250CP	IPP65R280C6	IPS118N10N G	IPW60R165CP
IPP60R280C6	IPP65R280E6	IPS12CN10L G	IPW60R190C6
IPP60R280E6	IPP65R310CFD	IPS135N03L G	IPW60R190E6
IPP60R299CP	IPP65R310CFDA	IPS50R520CP	IPW60R199CP
IPP60R380C6	IPP65R380C6	IPT004N03L	IPW60R250CP
IPP60R380E6	IPP65R380E6	IPT007N06N	IPW60R280C6
IPP60R385CP	IPP65R420CFD	IPT020N10N3	IPW60R280E6
IPP60R520C6	IPP65R600C6	IPT059N15N3	IPW65R019C7
IPP60R520E6	IPP65R600E6	IPU135N08N3 G	IPW65R037C6
IPP60R600C6	IPP65R660CFD	IPU50R1K4CE	IPW65R041CFD
IPP60R600E6	IPP65R660CFDA	IPU50R2K0CE	IPW65R045C7
IPP60R950C6	IPP80CN10N G	IPU50R3K0CE	IPW65R048CFDA
IPP65R045C7	IPP90R1K0C3	IPU50R950CE	IPW65R065C7
IPP65R065C7	IPP90R1K2C3	IPW50R190CE	IPW65R070C6
IPP65R095C7	IPP90R340C3	IPW50R199CP	IPW65R080CFD
IPP65R110CFD	IPP90R500C3	IPW50R280CE	IPW65R080CFDA

# Multisim 14.0 Education Components

---

IPW65R095C7	IR2101SPBF	IR2118PBF	IRF1010NS
IPW65R110CFDA	IR2102PBF	IR2118SPBF	IRF1010ZPBF
IPW65R125C7	IR2102SPBF	IR2127PBF	IRF1010ZSPBF
IPW65R150CFDA	IR2103PBF	IR2127SPBF	IRF1010ZSTRLPBF
IPW65R190C6	IR2103SPBF	IR2128PBF	IRF1010ZSTRRPBF
IPW65R190C7	IR2104PBF	IR2128SPBF	IRF1310
IPW65R190CFDA	IR2104SPBF	IR21363JPBF	IRF1324S-7PPBF
IPW65R190E6	IR2106PBF	IR21363PBF	IRF1324STRL-7PP
IPW65R280C6	IR2106SPBF	IR21363SPBF	IRF1404ZPBF
IPW65R280E6	IR21084PBF	IR21365PBF	IRF250
IPW90R120C3	IR21084SPBF	IR21365SPBF	IRF2505S
IPW90R1K0C3	IR2108PBF	IR2136JPBF	IRF2804PBF
IPW90R1K2C3	IR2108SPBF	IR2136PBF	IRF2804SPBF
IPW90R340C3	IR21094PBF	IR2136SPBF	IRF2804STRLPBF
IPW90R500C3	IR21094SPBF	IR2181PBF	IRF2804STRRPBF
IPW90R800C3	IR2109PBF	IR2181SPBF	IRF2903ZSPBF
IPZ65R019C7	IR2109SPBF	IR2183PBF	IRF2903ZSTRLP
IPZ65R045C7	IR2110PBF	IR2183SPBF	IRF3205
IPZ65R065C7	IR2110SPBF	IR2184PBF	IRF3205S
IPZ65R095C7	IR2112PBF	IR2184SPBF	IRF3704ZSPBF
IR2010PBF	IR2112SPBF	IR2301PBF	IRF3707ZSPBF
IR2010S	IR2113PBF	IR2301SPBF	IRF3709ZSTRRPBF
IR2010SPBF	IR2113SPBF	IR2302PBF	IRF3710
IR2011PBF	IR2117PBF	IR2302SPBF	IRF3710S
IR2101PBF	IR2117SPBF	IRF1010N	IRF3805S-7PPBF

# Multisim 14.0 Education Components

---

IRF3805STRL-7PP	IRF6645TRPBF	IRF6898MTRPBF	IRF8513TRPBF
IRF4104PBF	IRF6646TRPBF	IRF7201	IRF8707PBF
IRF510	IRF6648TRPBF	IRF7403	IRF8707TRPBF
IRF520	IRF6655TRPBF	IRF7404	IRF8714PBF
IRF520N	IRF6668TRPBF	IRF7413	IRF8714TRPBF
IRF520NS	IRF6674TRPBF	IRF7495PBF	IRF8721PBF
IRF5210	IRF6710S2TRPBF	IRF7495TRPBF	IRF8721TRPBF
IRF5210S	IRF6711STRPBF	IRF7739L1TRPBF	IRF8734PBF
IRF530	IRF6712STRPBF	IRF7748L1TRPBF	IRF8734TRPBF
IRF5305	IRF6713STRPBF	IRF7749L1TRPBF	IRF8736PBF
IRF5305S	IRF6714MTRPBF	IRF7759L2TRPBF	IRF8736TRPBF
IRF530N	IRF6715MTRPBF	IRF7769L1TRPBF	IRF8788PBF
IRF530NS	IRF6716MTRPBF	IRF7779L2TRPBF	IRF8788TRPBF
IRF540	IRF6717MTRPBF	IRF7799L2TRPBF	IRF9310PBF
IRF540N	IRF6718L2TRPBF	IRF7815PBF	IRF9310TRPBF
IRF540NS	IRF6727MTRPBF	IRF7815TRPBF	IRF9317PBF
IRF541	IRF6775MTRPBF	IRF7855PBF	IRF9317TRPBF
IRF6201PBF	IRF6785MTRPBF	IRF7855TRPBF	IRF9321PBF
IRF6201TRPBF	IRF6795MTRPBF	IRF7907PBF	IRF9321TRPBF
IRF6613TRPBF	IRF6797MTRPBF	IRF7907TRPBF	IRF9328PBF
IRF6614TRPBF	IRF6798MTRPBF	IRF7946TRPBF	IRF9328TRPBF
IRF6616TRPBF	IRF6810STRPBF	IRF830	IRF9333PBF
IRF6641TRPBF	IRF6811STRPBF	IRF8302MTRPBF	IRF9333TRPBF
IRF6643TRPBF	IRF6893MTRPBF	IRF8327STRPBF	IRF9335PBF
IRF6644TRPBF	IRF6894MTRPBF	IRF840	IRF9335TRPBF

# Multisim 14.0 Education Components

---

IRF9362PBF	IRFB4615PBF	IRFH4253DTRPBF	IRFH8337TRPBF
IRF9362TRPBF	IRFB4620PBF	IRFH5006TRPBF	IRFHM4226TRPBF
IRF9383MTRPBF	IRFB5615PBF	IRFH5010TRPBF	IRFHM4231TRPBF
IRF9389PBF	IRFB5620PBF	IRFH5020TRPBF	IRFHM4234TRPBF
IRF9389TRPBF	IRFB7430PBF	IRFH5025TRPBF	IRFHM792TRPBF
IRF9395MTRPBF	IRFB7434PBF	IRFH5106TRPBF	IRFHM8235TRPBF
IRF9530	IRFB7437PBF	IRFH5110TRPBF	IRFHM830DTRPBF
IRFB3004PBF	IRFB7440PBF	IRFH5204TRPBF	IRFHM830TRPBF
IRFB3006PBF	IRFB7446PBF	IRFH5206TRPBF	IRFHM831TRPBF
IRFB3077PBF	IRFB7530PBF	IRFH5207TRPBF	IRFHM8326TRPBF
IRFB3206PBF	IRFB7534PBF	IRFH5210TRPBF	IRFHM8330TRPBF
IRFB3207ZPBF	IRFB7537PBF	IRFH5215TRPBF	IRFHM8334TRPBF
IRFB3256PBF	IRFB7540PBF	IRFH5301TRPBF	IRFHM8337TRPBF
IRFB3306PBF	IRFB7545PBF	IRFH5302TRPBF	IRFHM8363TRPBF
IRFB3307ZPBF	IRFB7546PBF	IRFH5304TRPBF	IRFHM9391TRPBF
IRFB4020PBF	IRFE130	IRFH5406TRPBF	IRFHS8242TRPBF
IRFB4110PBF	IRFF110	IRFH6200TRPBF	IRFHS8342TRPBF
IRFB4115PBF	IRFG110	IRFH7107TRPBF	IRFHS9301TRPBF
IRFB4137PBF	IRFH4201TRPBF	IRFH7185TRPBF	IRFHS9351TRPBF
IRFB4227PBF	IRFH4210DTRPBF	IRFH8201TRPBF	IRFI1010N
IRFB4229PBF	IRFH4210TRPBF	IRFH8318TRPBF	IRFI3306GPBF
IRFB4310ZPBF	IRFH4213DTRPBF	IRFH8324TRPBF	IRFI3710
IRFB4321PBF	IRFH4213TRPBF	IRFH8325TRPBF	IRFI4410ZPBF
IRFB4332PBF	IRFH4234TRPBF	IRFH8330TRPBF	IRFI520N
IRFB4610PBF	IRFH4251DTRPBF	IRFH8334TRPBF	IRFI5210

# Multisim 14.0 Education Components

---

IRFI5305	IRFP2907ZPBF	IRFR3704ZTRPBF	IRFS3307ZTRRPBF
IRFI530N	IRFP3006PBF	IRFR3910	IRFS4010-7PPBF
IRFI540N	IRFP3710	IRFR4105	IRFS4010PBF
IRFI7536GPBF	IRFP4332PBF	IRFR4105ZPBF	IRFS4010TRL7PP
IRFI840G	IRFP4368PBF	IRFR4105ZTRPBF	IRFS4010TRLPBF
IRFI840GLC	IRFP4468PBF	IRFR48ZPBF	IRFS4010TRRPBF
IRFIZ44N	IRFP4568PBF	IRFR48ZTRLPBF	IRFS4115PBF
IRFIZ46N	IRFP4668PBF	IRFR48ZTRPBF	IRFS4115TRLPBF
IRFIZ48N	IRFP4768PBF	IRFR825PBF	IRFS4127PBF
IRFM140	IRFP5210	IRFR825TRPBF	IRFS4127TRLPBF
IRFM150	IRFP7430PBF	IRFS3004-7PPBF	IRFS4227PBF
IRFM9140	IRFP7530PBF	IRFS3004PBF	IRFS4227TRLPBF
IRFML8244TRPBF	IRFP7537PBF	IRFS3004TRL7PP	IRFS4321-7PPBF
IRFN054	IRFPG40	IRFS3004TRLPBF	IRFS4321TRL7PP
IRFP044N	IRFR110	IRFS3006-7PPBF	IRFS7430-7PPBF
IRFP048N	IRFR1205	IRFS3006TRL7PP	IRFS7430PBF
IRFP054N	IRFR120N	IRFS3107-7PPBF	IRFS7430TRL7PP
IRFP064	IRFR120ZPBF	IRFS3107TRL7PP	IRFS7430TRLPBF
IRFP064N	IRFR120ZTRPBF	IRFS3206PBF	IRFS7434-7PPBF
IRFP140N	IRFR2307ZPBF	IRFS3206TRRPBF	IRFS7434PBF
IRFP2410	IRFR2307ZTRLPBF	IRFS3207ZPBF	IRFS7434TRL7PP
IRFP244	IRFR2607ZPBF	IRFS3306PBF	IRFS7434TRLPBF
IRFP250	IRFR2607ZTRPBF	IRFS3306TRLPBF	IRFS7530PBF
IRFP260	IRFR3704ZPBF	IRFS3307ZPBF	IRFS7530TRLPBF
IRFP264	IRFR3704ZTRLPBF	IRFS3307ZTRLPBF	IRFS7534PBF

# Multisim 14.0 Education Components

---

IRFS7534TRLPBF	IRFZ44NS	IRG4BC40UPBF	IRG4PC50WPBF
IRFS7537PBF	IRFZ46N	IRG4BC40W	IRG4PF50WPBF
IRFS7537TRLPBF	IRFZ46NS	IRG4BC40WPBF	IRG4PH20KPBF
IRFS7540PBF	IRFZ48N	IRG4MC30F	IRG4PH50SPBF
IRFS7540TRLPBF	IRFZ48NS	IRG4MC40U	IRG4PH50UDPBF
IRFSL3004PBF	IRFZ48ZSPBF	IRG4MC50F	IRG4PH50UPBF
IRFSL4115PBF	IRG4BC10KDPBF	IRG4MC50U	IRG4PSC71KDPBF
IRFSL7430PBF	IRG4BC10U	IRG4PC30KDPBF	IRG4PSC71KPBF
IRFSL7530PBF	IRG4BC10UD	IRG4PC30KPBF	IRG4PSC71UPBF
IRFSL7534PBF	IRG4BC10UDPBF	IRG4PC30U	IRG4RC10K
IRFSL7537PBF	IRG4BC15UD	IRG4PC30UDPBF	IRG4RC10KD
IRFSL7540PBF	IRG4BC15UDPBF	IRG4PC30UPBF	IRG4RC10U
IRFU110	IRG4BC20FDPBF	IRG4PC40FPBF	IRG4RC10UD
IRFU1205	IRG4BC20SDPBF	IRG4PC40SPBF	IRG4RC10UDPBF
IRFU120N	IRG4BC20SD-SPBF	IRG4PC40UD-EPBF	IRG4RC10UDTRLP
IRFU2605	IRG4BC20U	IRG4PC40UDPBF	IRG4RC10UDTRP
IRFU3710ZPBF	IRG4BC20UDPBF	IRG4PC40UPBF	IRG4RC10UDTRRP
IRFU3910	IRG4BC20UPBF	IRG4PC50FD-EPBF	IRG4RC10UTRPBF
IRFU4105	IRG4BC30FPBF	IRG4PC50FDPBF	IRG4RC20FPBF
IRFU4105ZPBF	IRG4BC30KDPBF	IRG4PC50KDPBF	IRG4RC20FTRLPBF
IRFU48ZPBF	IRG4BC30UDPBF	IRG4PC50KPBF	IRG4RC20FTRPBF
IRFZ24N	IRG4BC30UPBF	IRG4PC50SPBF	IRG7PH46UD-EP
IRFZ24NS	IRG4BC40S	IRG4PC50UD-EPBF	IRG7PH46UDPBF
IRFZ34N	IRG4BC40SPBF	IRG4PC50UDPBF	IRG7PH46U-EP
IRFZ44N	IRG4BC40U	IRG4PC50UPBF	IRG7PH46UPBF



# Multisim 14.0 Education Components

---

IRG7PSH73K10PBF	IRGP4063D-EPBF	IRL2203	IRL7833SPBF
IRGB15B60KDPBF	IRGP4063DPBF	IRL2203NS	IRL7833STRLPBF
IRGB20B60PD1PBF	IRGP4068D-EPBF	IRL2203S	IRL8113PBF
IRGB30B60KPBF	IRGP4068DPBF	IRL2505	IRL8113SPBF
IRGB4045DPBF	IRGP50B60PD1PBF	IRL2505S	IRL8113STRLPBF
IRGB4059DPBF	IRGPC20F	IRL2703	IRLB3034PBF
IRGB4060DPBF	IRGPC20U	IRL2703S	IRLB3036PBF
IRGB4061DPBF	IRGPC40K	IRL2910	IRLB8748PBF
IRGB4062DPBF	IRGPC40UD2	IRL2910S	IRLH5034TRPBF
IRGB4B60KD1PBF	IRGPC50K	IRL3103	IRLH5036TRPBF
IRGB5B120KDPBF	IRGPC50M	IRL3103S	IRLHM620TRPBF
IRGB8B60KPBF	IRGPH40K	IRL3303	IRLHS2242TRPBF
IRGBC20F	IRGPH50K	IRL3303S	IRLHS6242TRPBF
IRGBC20K	IRGPH50M	IRL3705	IRLHS6276TRPBF
IRGBC20S	IRGPS40B120UDP	IRL3705N	IRLHS6342TRPBF
IRGBC20U	IRGPS60B120KDP	IRL3705NS	IRLHS6376TRPBF
IRGBC30F	IRGS15B60KDPBF	IRL3803	IRLI2203G
IRGBC30K	IRGS30B60KPBF	IRL3803S	IRLI2203N
IRGBC30UD2	IRGS4B60KD1PBF	IRL530N	IRLI2505
IRGLC60KD1	IRGS8B60KPBF	IRL530NS	IRLI2703
IRGP20B120UD-EP	IRGS8B60KTRLPBF	IRL540	IRLI2910
IRGP30B120KD-EP	IRGSL15B60KDPBF	IRL6283MTRPBF	IRLI3103
IRGP30B60KD-EP	IRGSL30B60KPBF	IRL6297SDTRPBF	IRLI3303
IRGP4062D-EPBF	IRGSL4B60KD1PBF	IRL6342PBF	IRLI3803
IRGP4062DPBF	IRL1404ZPBF	IRL6342TRPBF	IRLI530N

# Multisim 14.0 Education Components

---

IRLIZ24N	IRLR2905ZTRLPBF	IRLR8729PBF	IRLZ44N
IRLIZ34N	IRLR2905ZTRPBF	IRLR8729TRLPBF	J108
IRLL3303	IRLR3103	IRLR8729TRPBF	J109
IRLML0030TRPBF	IRLR3110ZPBF	IRLR8743PBF	J110
IRLML0040TRPBF	IRLR3110ZTRLPBF	IRLR8743TRLPBF	J111
IRLML0060TRPBF	IRLR3110ZTRPBF	IRLR8743TRPBF	J112
IRLML0100TRPBF	IRLR3110ZTRRPBF	IRLS4030-7PPBF	J113
IRLML2030TRPBF	IRLR3303	IRLS4030PBF	J174
IRLML2060TRPBF	IRLR3636PBF	IRLS4030TRL7PP	J175
IRLML2244TRPBF	IRLR3636TRLPBF	IRLS4030TRLPBF	J176
IRLML6244TRPBF	IRLR3636TRPBF	IRLSL4030PBF	J177
IRLML6246TRPBF	IRLR3705ZPBF	IRLTS2242TRPBF	J210
IRLML6346TRPBF	IRLR3705ZTRPBF	IRLU024N	J211
IRLML9301TRPBF	IRLR3717PBF	IRLU2703	J212
IRLML9303TRPBF	IRLR3717TRPBF	IRLU2705	J2N5902
IRLP150	IRLR3717TRRPBF	IRLU2905	J2N5904
IRLP2203	IRLR6225PBF	IRLU2905ZPBF	J2N5905
IRLP2505	IRLR6225TRPBF	IRLU3103	J2N5906
IRLP3705	IRLR7807ZPBF	IRLU3110ZPBF	J2N5907
IRLP3803	IRLR7807ZTRPBF	IRLU3303	J2N5908
IRLR024N	IRLR8256PBF	IRLU3636PBF	J2N5909
IRLR2703	IRLR8256TRPBF	IRLU3705ZPBF	J2N5911
IRLR2705	IRLR8726PBF	IRLU8743PBF	J2N5912
IRLR2905	IRLR8726TRLPBF	IRLZ34N	J2N6483
IRLR2905ZPBF	IRLR8726TRPBF	IRLZ34NS	J2N6484

# Multisim 14.0 Education Components

---

J2N6485	JFET_N	LATTICE- ispDOWNLOAD- USB-HDR	LED_ir
J308	JFET_P		LED_orange
J309	JK_FF	LC03-6R2G	LED_red
J310	JK_FF_NEGSR	LCD_DISPLAY_08x1	LED_RED_RATED
J401	KT88	LCD_DISPLAY_08x2	LED_yellow
J402	L1	LCD_DISPLAY_10x2	LED_YELLOW_RATE D
J403	L2	LCD_DISPLAY_16x1	Led1_Red
J404	L2081	LCD_DISPLAY_16x2	Led2_Yellow
J405	L2082	LCD_DISPLAY_16x4	Led3_Green
J406	L2083	LCD_DISPLAY_20x2	LF13741H
J410	L88008	LCD_DISPLAY_20x4	LF147D/883
J411	L88012	LCD_DISPLAY_24x2	LF147J
J412	L88016	LCD_DISPLAY_30x2	LF147J/883
JAN2N2907A	LA_CARRY_GEN	LCD_DISPLAY_32x2	LF155AH
JAN2N3700	LA_CARRY_GEN	LCD_DISPLAY_40x2	LF155AH/883
JAN2N4029	LAMP	LCD_DISPLAY_4DIGI T	LF155H
JAN2N4033	LAMP_VIRTUAL		LF155H/883
JANTX2N2907A	LATCH_D	LD102A	LF156AH
JANTX2N3700	LATCH_D2	LD103A	LF156AH/883
JANTX2N4029	LATCH_D4_SR_OE	LD106	LF156H
JANTX2N4033	LATCH_SR	LED	LF156H/883
JANTXV2N2907A	LATTICE- ispDOWNLOAD- HDR	LED_blue	LF157AH/883
JANTXV2N3700		LED_BLUE_RATED	LF157H/883
JANTXV2N4029		LED_green	LF255H
JANTXV2N4033		LED_GREEN_RATED	

# Multisim 14.0 Education Components

---

LF256H	LF356H	LF412CD	LF444AMD
LF257H	LF356M	LF412CH	LF444CD
LF347BD	LF356N	LF412CJG	LF444CJ
LF347BN	LF357AH	LF412CN	LF444CM
LF347D	LF357BN	LF412CP	LF444CN
LF347M	LF357H	LF412MH	LF444MD/883
LF347N	LF357M	LF412MH/883	LF451CM
LF351D	LF357N	LF412MJ/883	LF453CM
LF351M	LF400	LF441AMH	LH0003CH
LF351N	LF411ACH	LF441CD	LH0003H
LF351P	LF411ACN	LF441CH	LH0004CH
LF353D	LF411AMH	LF441CJ	LH0004H
LF353H	LF411CD	LF441CM	LH0004H-MIL
LF353M	LF411CH	LF441CN	LH0021CK
LF353N	LF411CJG	LF441MH/883	LH0021K
LF353P	LF411CN	LF442ACN	LH0022CD
LF355AH	LF411CP	LF442AMH	LH0022CH
LF355BM	LF411ID	LF442CD	LH0024CH
LF355BN	LF411IP	LF442CH	LH0024H
LF355H	LF411MH	LF442CJ	LH0024H-MIL
LF355M	LF411MH/883	LF442CM	LH0032CG
LF355N	LF411MWG/883	LF442CN	LH0032G
LF356AH	LF412ACH	LF442MH	LH0032G/883
LF356BM	LF412ACN	LF442MH/883	LH0041CG
LF356BN	LF412AMH	LF444ACN	LH0041CJ

# Multisim 14.0 Education Components

---

LH0041G	LM101AF/883	LM107JG	LM108JG
LH0042CH	LM101AFK	LM107JG/883	LM108JG/883
LH0042H	LM101AFK/883	LM107U	LM108L
LH0042H-MIL	LM101AH	LM107W	LM108P
LH0062CD	LM101AH/883	LM107W/883	LM10BH
LH0062CH	LM101AJ	LM108AD	LM10BLH
LH0062D	LM101AJ/883	LM108AH	LM10CH
LH0062H	LM101AJ-14	LM108AH/883	LM10CLH
LH0101ACK	LM101AJ-14/883	LM108AJ	LM10CLN
LH0101AK	LM101AJ8	LM108AJ/883	LM10CLN8
LH0101AK-MIL	LM101AJG	LM108AJ-8	LM10CLWM
LH0101CK	LM101AJG/883	LM108AJ-8/883	LM10CN
LH0101K	LM101AP	LM108AJG	LM10CN8
LH0101K-MIL	LM101AU	LM108AL	LM10CWM
LH1041G	LM101AU/883	LM108AP	LM10H
LH4161	LM101AW	LM108D	LM10H/883
LH4162	LM101AW/883	LM108D/883	LM111E
LHV870LC/NOPB	LM101D	LM108H	LM111E/883
LIMIT_NC	LM101F	LM108H/883	LM111H
LIMIT_NO	LM101F/883	LM108J	LM111J-14
LINKSYS-WRT54G- HD	LM101H	LM108J/883	LM111J-8
LM101AD	LM101H/883	LM108J8	LM111W
LM101AD/883	LM101J-14	LM108J-8	LM112H
LM101AF	LM101J-14/883	LM108J8/883	LM112H/883
	LM107J	LM108J-8/883	LM117HVH

# Multisim 14.0 Education Components

---

LM117HVKSTL/883	LM124AW/883	LM144H/883	LM1877N-9
LM118D	LM124AWG/883	LM146J	LM202H
LM118FK	LM124D	LM146J/883	LM207D
LM118H	LM124E	LM149J	LM207H
LM118H/883	LM124E/883	LM149J/883	LM207J
LM118J	LM124FK	LM158AD	LM207P
LM118J/883	LM124J	LM158AFK	LM208AD
LM118J8	LM124J/883	LM158AH	LM208AH
LM118J-8	LM124N	LM158AH/883	LM208AJ
LM118J8/883	LM124W	LM158AJ	LM208AJ-8
LM118J-8/883	LM124W/883	LM158AJG	LM208AN
LM118JG	LM12CLK	LM158AN	LM208AP
LM118L	LM12LK	LM158AP	LM208D
LM118P	LM13600AN	LM158AWG/883	LM208H
LM11CH	LM13600M	LM158D	LM208J
LM11CLH	LM13600N	LM158FK	LM208J-8
LM11CLN	LM13700AN	LM158H	LM208N
LM11H	LM13700M	LM158J	LM208P
LM124AD	LM13700N	LM158JG	LM211H
LM124AE	LM139AJ	LM158N	LM211J-8
LM124AE/883	LM139AW	LM158P	LM211M
LM124AFK	LM139E	LM160H	LM212H
LM124AJ	LM139J	LM160J	LM216AD
LM124AJ/883	LM139W	LM160J-14	LM216AF
LM124AN	LM144H	LM1877M-9	LM216AH

# Multisim 14.0 Education Components

---

LM216D	LM239J	LM2901VDTBR2G	LM2904DG
LM216F	LM239NG	LM2901VNG	LM2904DMR2G
LM216H	LM246J	LM2902DG	LM2904DR2G
LM218D	LM258AD	LM2902DR2G	LM2904ITP
LM218H	LM258AH	LM2902DTBG	LM2904M
LM218JG	LM258AJG	LM2902DTBR2G	LM2904N
LM218P	LM258AN	LM2902M	LM2904NG
LM221H	LM258AP	LM2902MT	LM2904P
LM224AD	LM258D	LM2902N	LM2904PW
LM224AJ	LM258DG	LM2902NG	LM2904QD
LM224AN	LM258DMR2G	LM2902VD	LM2904QP
LM224AP	LM258DR2G	LM2902VDG	LM2904VD
LM224D	LM258H	LM2902VDR2G	LM2904VDG
LM224DG	LM258JG	LM2902VDTBG	LM2904VDMR2G
LM224DR2G	LM258N	LM2902VDTBR2G	LM2904VDR2G
LM224DTBG	LM258NG	LM2902VN	LM2904VN
LM224DTBR2G	LM258P	LM2903DG	LM2904VNG
LM224J	LM2878P	LM2903DMR2G	LM2924M
LM224N	LM2900N	LM2903DR2	LM2924N
LM224NG	LM2901DG	LM2903DR2G	LM293D
LM224P	LM2901DR2G	LM2903NG	LM293DG
LM239AJ	LM2901DTBR2G	LM2904ADMR2G	LM293DMR2G
LM239DG	LM2901NG	LM2904AN	LM293DR2G
LM239DR2G	LM2901VDG	LM2904ANG	LM301AD
LM239DTBR2G	LM2901VDR2G	LM2904D	LM301AJ8

# Multisim 14.0 Education Components

---

LM301AP	LM318J8	LM324DTBR2G	LM348D
LM3046M	LM318J-8	LM324J	LM348N
LM307D	LM318M	LM324M	LM348PW
LM307N	LM318N	LM324MT	LM358AD
LM307P	LM318N8	LM324N	LM358ADR2G
LM308AD	LM318P	LM324NG	LM358AH
LM308AH	LM318S8	LM324P	LM358AJG
LM308AJ	LM321AH	LM324PWLE	LM358AM
LM308AJ-8	LM321H	LM324x2DBLE	LM358AN
LM308AN	LM324AD	LM3301N	LM358AP
LM308AN8	LM324ADG	LM3302N	LM358BP
LM308D	LM324ADR2G	LM339AJ	LM358D
LM308H	LM324ADTBG	LM339AM	LM358DB
LM308J	LM324ADTBR2G	LM339AN	LM358DG
LM308J-8	LM324AJ	LM339DG	LM358DMR2G
LM308M	LM324AM	LM339DR2G	LM358DR2G
LM308N	LM324AN	LM339DTBR2G	LM358H
LM308N8	LM324ANG	LM339J	LM358J
LM311H	LM324AP	LM339M	LM358JG
LM311M	LM324APWLE	LM339N	LM358M
LM311N	LM324D	LM339NG	LM358N
LM311N-14	LM324DBLE	LM344H	LM358NG
LM312H	LM324DG	LM346J	LM358P
LM318D	LM324DR2G	LM346M	LM358PW
LM318H	LM324DTBG	LM346N	LM358TP



# Multisim 14.0 Education Components

---

LM359J	LM555CN	LM6142AMJ-QML	LM6165J
LM359M	LM556CM	LM6142BIM	LM6165J/883
LM359N	LM556CN	LM6142BIN	LM6165W/883
LM3875TF/NOPB	LM607ACH	LM6144AIM	LM6165WG/883
LM3900D	LM607ACN	LM6144AIN	LM6171AIM
LM3900M	LM607AMH	LM6144BIM	LM6171BIM
LM3900N	LM607BCH	LM6144BIN	LM6171BIN
LM393DG	LM607BCN	LM6152ACM	LM6172AMJFQML
LM393DMR2G	LM607BMH	LM6152BCM	LM6172AMWGFQ ML
LM393DR2G	LM607CH	LM6161E/883	LM6172IM
LM393NG	LM607CN	LM6161J	LM6172IN
LM4250CH	LM6118E/883	LM6161J/883	LM6181IM
LM4250CM	LM6118J/883	LM6161W/883	LM6181IN
LM4250CN	LM6118N	LM6161WG/883	LM6211MF
LM4250H	LM6132AIM	LM6162E/883	LM6218AN
LM4250J	LM6132AIN	LM6162J/883	LM6218AWM
LM4250J-MIL	LM6132BIM	LM6162N	LM6218N
LM4562HA	LM6132BIN	LM6162W/883	LM6218WM
LM4562MA	LM6134AIM	LM6162WG/883	LM6261J
LM4562NA	LM6134AIN	LM6164E/883	LM6261M
LM4871LD	LM6134BIM	LM6164J	LM6261N
LM4871M	LM6134BIN	LM6164J/883	LM6262M
LM4871MM/NOPB	LM6142AIM	LM6164W/883	LM6262N
LM4871MX	LM6142AIN	LM6164WG/883	LM6264J
LM555CM	LM6142AMJ-MLS	LM6165E/883	

# Multisim 14.0 Education Components

---

LM6264N	LM637ACH	LM7171AIN	LM741AJ-14/883
LM6265J	LM637AMH	LM7171AMJFQML	LM741CH
LM6265N	LM637BCH	LM7171BIM	LM741CJ
LM627ACH	LM637BMH	LM7171BIN	LM741CM
LM627AMH	LM637CH	LM723CN	LM741CN
LM627BCH	LM637CN	LM723E	LM741EH
LM627BMH	LM709AH	LM723H	LM741EN
LM627CH	LM709CH	LM725AH	LM741H
LM627CN	LM709CN	LM725AH/883	LM741H/883
LM6310IM	LM709CN-8	LM725CH	LM741J
LM6310IN	LM709H	LM725CN	LM741J/883
LM6311IM	LM710AMJ	LM725H	LM741J-14/883
LM6311IN	LM710AMW	LM725H/883	LM741W/883
LM6313N	LM710CH	LM7301IM	LM747AH
LM6317IM	LM710CN	LM7301IM5	LM747AJ
LM6317IN	LM710H	LM7321MA	LM748CH
LM6361J	LM7121IM	LM7321MF	LM748CJ
LM6361M	LM7121IM5	LM7322MA	LM748CN
LM6361N	LM7131ACM	LM7322MM	LM748H
LM6362M	LM7131ACM5	LM7332MA	LM759CH
LM6362N	LM715CH	LM7332MM	LM759CP
LM6364M	LM715CJ	LM7341MF	LM759H/883
LM6364N	LM715MH	LM7372IMA	LM759MH
LM6365M	LM715MJ	LM7372MR	LM7805CT
LM6365N	LM7171AIM	LM741AH/883	LM7809CT

# Multisim 14.0 Education Components

---

LM7812CT	LMC6032IM	LMC6061IM	LMC6084AIN
LM7815CT	LMC6032IN	LMC6061IN	LMC6084AMN
LM7818CT	LMC6034IM	LMC6062AIM	LMC6084IM
LM7824CT	LMC6035IBP	LMC6062AIN	LMC6084IN
LM7905CT	LMC6035IM	LMC6062AMJ/883	LMC6442AIM
LM7909CT	LMC6035IMM	LMC6062AMN	LMC6442IM
LM7912CT	LMC6035ITL	LMC6062IM	LMC6442IN
LM7915CT	LMC6036IM	LMC6062IN	LMC6462AIM
LM7918CT	LMC6036IMT	LMC6064AIM	LMC6462AIN
LM7924CT	LMC6041AIM	LMC6064AIN	LMC6462AMN
LM8261M5	LMC6041AIN	LMC6064AMJ/883	LMC6462BIM
LM8272MM	LMC6041IM	LMC6064AMN	LMC6462BIN
LM833D	LMC6041IN	LMC6064IM	LMC6462IM
LM833DG	LMC6042AIM	LMC6064IN	LMC6462IN
LM833DR2G	LMC6042AIN	LMC6081AIM	LMC6464AIM
LM833NG	LMC6042IM	LMC6081AIN	LMC6464AIN
LMC555CH	LMC6042IN	LMC6081AMN	LMC6464AMN
LMC555CM	LMC6044AIM	LMC6081IM	LMC6464AMWG- QML
LMC555CN	LMC6044AIN	LMC6081IN	LMC6464BIM
LMC6001AIH	LMC6044IM	LMC6082AIM	LMC6464BIN
LMC6001AIN	LMC6044IN	LMC6082AIN	LMC6464IM
LMC6001BIH	LMC6061AIM	LMC6082AMN	LMC6464IN
LMC6001BIN	LMC6061AIN	LMC6082IM	LMC6482AIM
LMC6022IM	LMC6061AMJ/883	LMC6082IN	LMC6482AIN
LMC6024IM	LMC6061AMN	LMC6084AIM	

# Multisim 14.0 Education Components

---

LMC6482AMJ/883	LMC6574AIM	LMC6681AIN	LMC7211BIM5
LMC6482IM	LMC6574AIN	LMC6681BIM	LMC7215IM
LMC6482IMM	LMC6574BIM	LMC6681BIN	LMC7215IM5
LMC6482IN	LMC6574BIN	LMC6682AIM	LMC7221AIM
LMC6482MN	LMC6582AIM	LMC6682AIN	LMC7221AIM5
LMC6484AIM	LMC6582AIN	LMC6682BIM	LMC7221BIM
LMC6484AIN	LMC6582BIM	LMC6682BIN	LMC7221BIM5
LMC6484AMJ/883	LMC6582BIN	LMC6684AIM	LMC7225IM5
LMC6484AMWG/883	LMC6584AIM	LMC6684AIN	LMC8101BP
	LMC6584AIN	LMC6684BIM	LMC8101MM
LMC6484IM	LMC6584BIM	LMC6684BIN	LMC8101TP
LMC6484IN	LMC6584BIN	LMC6762AIM	LME49600TS/NOPB
LMC6484MN	LMC660AIM	LMC6762BIM	LME49710HA
LMC6492AEM	LMC660AIN	LMC6772AIM	LME49710MA
LMC6492AEN	LMC660AMD	LMC6772AIMM	LME49710NA
LMC6492BEM	LMC660AMJ/883	LMC6772BIM	LME49713HA/NOPB
LMC6492BEN	LMC660CM	LMC6772BIN	
LMC6494AEM	LMC660CN	LMC7101AIM5	LME49713MA/NOPB
LMC6494AEN	LMC662AIM	LMC7101AIN	LME49720HA
LMC6494BEM	LMC662AIN	LMC7101BIM5	LME49720MA
LMC6494BEN	LMC662AMD	LMC7101BIN	LME49720NA
LMC6572AIM	LMC662AMJ/883	LMC7111BIM5	LME49721MA/NOPB
LMC6572AIN	LMC662CM	LMC7211AIM	
LMC6572BIM	LMC662CN	LMC7211AIM5	LME49740MA
LMC6572BIN	LMC6681AIM	LMC7211BIM	LME49740NA

# Multisim 14.0 Education Components

---

LME49990MA/NOPB	LMH6609MF	LMH6644MT	LMH6720MA
	LMH6611MK	LMH6645MA	LMH6720MF
LMH6321MR	LMH6612MA	LMH6645MF	LMH6722J-QML
LMH6321TS	LMH6618MK	LMH6646MA	LMH6722MA
LMH6502MA	LMH6619MA	LMH6646MM	LMH6722MT
LMH6502MT	LMH6622MA	LMH6647MA	LMH6723MA
LMH6503MA	LMH6622MM	LMH6647MF	LMH6723MF
LMH6503MT	LMH6624J-QML	LMH6655MA	LMH6733MQ
LMH6505MA	LMH6624MA	LMH6655MM	LMH6738MQ
LMH6505MM	LMH6624MF	LMH6657MF	LMH6739MQ
LMH6521SQ/NOPB	LMH6628JFQML	LMH6657MG	LMP2011MA
LMH6550MA	LMH6628MA	LMH6672MA	LMP2011MF
LMH6550MM	LMH6628WGFQML	LMH6672MR	LMP2015MA
LMH6551MA	LMH6629MF	LMH6702J-QML	LMP2015MF
LMH6551MM	LMH6629SD	LMH6702MA	LMP2016MA
LMH6552MA	LMH6639MA	LMH6702MF	LMP2016MM
LMH6552SD	LMH6639MF	LMH6703MA	LMP2021MA
LMH6553MR	LMH6642MA	LMH6703MF	LMP2021MF
LMH6553SD	LMH6642MF	LMH6714J-QML	LMP2022MA
LMH6554LE	LMH6642MFXEP	LMH6714MA	LMP2022MM
LMH6555SQ	LMH6643MA	LMH6714MF	LMP2231AMA
LMH6559MA	LMH6643MAXEP	LMH6715JFQML	LMP2231AMF
LMH6559MF	LMH6643MM	LMH6715MA	LMP2231BMA
LMH6601MG	LMH6644MA	LMH6718MA	LMP2231BMF
LMH6609MA	LMH6644MAXEP	LMH6720J-QML	LMP2232AMA

# Multisim 14.0 Education Components

---

LMP2232AMM	LMP7718MM	LMP8674MA/NOPB	LMV611MF/NOPB
LMP2232BMA	LMP7731MA	LMV2011MA	LMV611MG/NOPB
LMP2232BMM	LMP7731MF	LMV2011MF	LMV612MA/NOPB
LMP2234AMA	LMP7732MA	LMV321M5	LMV612MM/NOPB
LMP2234AMT	LMP7732MM	LMV321M7	LMV614MA/NOPB
LMP2234BMA	LMP8270MA	LMV324M	LMV614MT/NOPB
LMP2234BMT	LMP8271MA	LMV324MT	LMV641MA
LMP7300MA	LMP8272MA	LMV331M5	LMV641MG
LMP7300MM	LMP8275MA	LMV331M7	LMV651MG
LMP7701MA	LMP8276MA	LMV339M	LMV652MM
LMP7701MF	LMP8277MA	LMV339MT	LMV654MT
LMP7702MA	LMP8601MA	LMV342MA	LMV711M6
LMP7702MM	LMP8601QMA	LMV342MM	LMV716MM
LMP7704MA	LMP8602MA	LMV358M	LMV7219M5
LMP7704MT	LMP8602MM	LMV358MM	LMV7219M7
LMP7707MF	LMP8602QMA	LMV393M	LMV721M5
LMP7708MM	LMP8602QMM	LMV393MM	LMV721M7
LMP7709MT	LMP8603MA	LMV551MG	LMV7271MF
LMP7711MK	LMP8603MM	LMV552MM	LMV7271MG
LMP7712MM	LMP8603QMA	LMV554MT	LMV7291MG
LMP7715MF	LMP8603QMM	LMV601MG/NOPB	LMV751M5
LMP7716MM	LMP8645HVMMK	LMV602MA/NOPB	LMV761MA
LMP7717MA	LMP8645MK	LMV602MM/NOPB	LMV761MF
LMP7717MF	LMP8671MA/NOPB	LMV604MA/NOPB	LMV771MG
LMP7718MA	LMP8672MA/NOPB	LMV604MT/NOPB	LMV772MA

# Multisim 14.0 Education Components

---

LMV772MM	LMV851MG	LOG102AID	LP324N
LMV772QMM	LMV852MM	LOG104AID	LP339D
LMV774MT	LMV854MT	LOG112AID	LP339J
LMV791MK	LMV861MG	LOG114AIRGVR	LP339M
LMV792MM	LMV862MM	LOSSLESS_LINE_TYP E1	LP339N
LMV793MA	LMV881LE/NOPB	LOSSLESS_LINE_TYP E2	LPC660AIM
LMV793MF	LMV931MF	LOSSLESS_LINE_TYP E2	LPC660AIN
LMV794MA	LMV931MG	LOSSY_TRANSMISSI ON_LINE	LPC660AMD
LMV794MM	LMV932MA	LP111JG	LPC660AMJ/883
LMV796MF	LMV932MM	LP124J	LPC660IM
LMV797MM	LMV934MA	LP211D	LPC661AIM
LMV821M5	LMV934MT	LP211JG	LPC661AIN
LMV821M7	LMV951MK	LP211P	LPC661AMN
LMV822M	LMV981BL	LP239D	LPC661IM
LMV822MM	LMV981MF	LP239J	LPC661IN
LMV824M	LMV981MG	LP239N	LPC662AIM
LMV824MT	LMV981TL	LP2901D	LPC662AIN
LMV831MG	LMX321AUK+	LP2901J	LPC662AMD
LMV832MM	LMX321AXK+	LP2901N	LPC662AMJ/883
LMV834MT	LMX324ASD+	LP2902M	LPC662IM
LMV841MG	LMX324AUD+	LP2902N	LPC662IN
LMV842MA	LMX358AKA+	LP311M	LPV321M5
LMV842MM	LMX358ASA+	LP311N	LPV321M7
LMV844MA	LMX358AUA+	LP324M	LPV324M
LMV844MT	LOG101AID		LPV324MT

# Multisim 14.0 Education Components

---

LPV358MM	LT1006AMJ8	LT1007ML	LT1013ACP
LPV358MX	LT1006CH	LT1007MP	LT1013AIP
LPV511MG	LT1006CJ8	LT1008CH	LT1013AMFK
LPV521MG	LT1006CN8	LT1008CN8	LT1013AMH
LT1001	LT1006MH	LT1008MH	LT1013AMJ8
LT1001ACH	LT1006MJ8	LT1008S8	LT1013AMP
LT1001ACJ8	LT1006S8	LT1010CDD	LT1013CH
LT1001ACN8	LT1007ACH	LT1010CH	LT1013CJ8
LT1001AMH/883	LT1007ACJ8	LT1010CN8	LT1013CN8
LT1001AMJ8/883	LT1007ACN8	LT1010CT	LT1013CP
LT1001CH	LT1007ACP	LT1010MH	LT1013DD
LT1001CJ8	LT1007AMH	LT1011CN8	LT1013DID
LT1001CN8	LT1007AMJ8	LT1011CS8	LT1013DIP
LT1001CS8	LT1007AMJG	LT1012	LT1013DMD
LT1001MH	LT1007AML	LT1012ACH	LT1013DMJG
LT1001MJ8	LT1007AMP	LT1012ACN8	LT1013DMP
LT1002ACJ	LT1007CDW	LT1012AMH	LT1013DN8
LT1002ACN	LT1007CH	LT1012CH	LT1013DP
LT1002AMJ	LT1007CJ8	LT1012CN8	LT1013IP
LT1002CJ	LT1007CN8	LT1012DH	LT1013MFK
LT1002CN	LT1007CP	LT1012DN8	LT1013MH
LT1002MJ	LT1007CS	LT1012MH	LT1013MJ8
LT1006ACH	LT1007MH	LT1012S8	LT1013MJG
LT1006ACJ8	LT1007MJ8	LT1013ACH	LT1013MP
LT1006AMH	LT1007MJG	LT1013ACJ8	LT1014ACJ



# Multisim 14.0 Education Components

---

LT1014AMJ	LT1022CH	LT1037AMJG	LT1056S8
LT1014CJ	LT1022CN8	LT1037AML	LT1057ACH
LT1014CN	LT1022MH	LT1037AMP	LT1057ACJ8
LT1014DN	LT1024ACN	LT1037CDW	LT1057ACN8
LT1014MJ	LT1024AMD	LT1037CH	LT1057AMH
LT1016CN8	LT1024CN	LT1037CJ8	LT1057AMJ8
LT1016CS8	LT1024MD	LT1037CN8	LT1057CH
LT1016IN8	LT1028	LT1037CP	LT1057CJ8
LT1016IS8	LT1028ACH	LT1037CS	LT1057CN8
LT1017CN8	LT1028ACJ8	LT1037MH	LT1057IS
LT1017CS8	LT1028ACN8	LT1037MJ8	LT1057MH
LT1017CSW	LT1028AMH	LT1037MJG	LT1057MJ8
LT1018CN8	LT1028AMJ8	LT1037ML	LT1057S
LT1018CS8	LT1028CH	LT1037MP	LT1058ACJ
LT1018CSW	LT1028CJ8	LT1055ACH	LT1058ACN
LT1021BCH-5	LT1028CN8	LT1055AMH	LT1058AMJ
LT1021BCN8-10	LT1028CS	LT1055CH	LT1058CJ
LT1021BCN8-5	LT1028MH	LT1055CN8	LT1058CMJ
LT1021BCN8-7	LT1028MJ8	LT1055MH	LT1058CN
LT1021BMH-10	LT1037ACH	LT1055S8	LT1077ACH
LT1021DCS8-10	LT1037ACJ8	LT1056ACH	LT1077ACJ8
LT1021DCS8-5	LT1037ACN8	LT1056AMH	LT1077ACN8
LT1021DCS8-7	LT1037ACP	LT1056CH	LT1077AIN8
LT1022ACH	LT1037AMH	LT1056CN8	LT1077AMH
LT1022AMH	LT1037AMJ8	LT1056MH	LT1077AMJ8

# Multisim 14.0 Education Components

---

LT1077CH	LT1084CP	LT1114S	LT1126CN8
LT1077CJ8	LT1084CT	LT1115CN8	LT1126CS8
LT1077CN8	LT1085CM	LT1115CS	LT1127CN
LT1077IN8	LT1085CT	LT1116CN8	LT1127CSW
LT1077IS8	LT1097CN8	LT1116CS8	LT1128CN8
LT1077MH	LT1097S8	LT1121CN8	LT1128CS8
LT1077MJ8	LT1101ACH	LT1121CS8	LT1129CQ
LT1077S8	LT1101ACJ8	LT1122ACJ8	LT1129CS8
LT1078ACH	LT1101ACN8	LT1122ACN8	LT1129CT
LT1078ACN8	LT1101AIN8	LT1122AMJ8	LT1167CN8
LT1078AMJ8	LT1101AMH	LT1122BCJ8	LT1167CS8
LT1078CN8	LT1101AMJ8	LT1122BCN8	LT1168CN8
LT1078IN8	LT1101CH	LT1122BMJ8	LT1168CS8
LT1078IS8	LT1101CJ8	LT1122CCJ8	LT1169CN8
LT1078MH	LT1101CN8	LT1122CCN8	LT1169CS8
LT1078MJ8	LT1101IN8	LT1122CMJ8	LT1178ACH
LT1078S8	LT1101MH	LT1122CS8	LT1178ACJ8
LT1079ACN	LT1101MJ8	LT1122DCJ8	LT1178ACN8
LT1079AM	LT1101S	LT1122DCN8	LT1178AMH
LT1079CN	LT1102ACN8	LT1122DMJ8	LT1178AMJ8
LT1079IN	LT1102CN8	LT1122DS8	LT1178CH
LT1079ISW	LT1102IN8	LT1124CN8	LT1178CJ8
LT1079MJ	LT1112S8	LT1124CS8	LT1178CN8
LT1079SW	LT1113ACN8	LT1125CN	LT1178IN8
LT1083CP	LT1113CS8	LT1125CSW	LT1178MH

# Multisim 14.0 Education Components

---

LT1178MJ8	LT1191CJ8	LT1206CN8	LT1214CS
LT1178S	LT1191CN8	LT1206CR	LT1215ACN8
LT1179ACJ	LT1191CS8	LT1206CS8	LT1215AMJ8
LT1179ACN	LT1191MJ8	LT1206CY	LT1215CN8
LT1179AMJ	LT1192CJ8	LT1207CS	LT1215CS8
LT1179CJ	LT1192CN8	LT1208CN8	LT1215MJ8
LT1179CN	LT1192CS8	LT1208CS8	LT1216CN
LT1179IN	LT1192MJ8	LT1209CN	LT1216CS
LT1179MJ	LT1193CJ8	LT1209CS	LT1217CN8
LT1179S	LT1193CN8	LT1210CR	LT1217CS8
LT1179SW	LT1193CS8	LT1210CS	LT1218CN8
LT1187CJ8	LT1193MJ8	LT1210CT7	LT1218CS8
LT1187CN8	LT1194CJ8	LT1211ACN8	LT1219CN8
LT1187CS8	LT1194CN8	LT1211AMJ8	LT1219CS8
LT1187MJ8	LT1194CS8	LT1211CN8	LT1220CN8
LT1189CJ8	LT1194MJ8	LT1211CS8	LT1220CS8
LT1189CN8	LT1195CJ8	LT1211MJ8	LT1220MJ8
LT1189CS8	LT1195CN8	LT1212CN	LT1221CN8
LT1189MJ8	LT1195CS8	LT1212CS	LT1221CS8
LT118AH	LT1195MJ8	LT1213ACN8	LT1221MJ8
LT118AJ8	LT1200	LT1213AMJ8	LT1222CN8
LT1190CJ8	LT1201CN8	LT1213CN8	LT1222IS8
LT1190CN8	LT1201CS8	LT1213CS8	LT1223CJ8
LT1190CS8	LT1202CN	LT1213MJ8	LT1223CN8
LT1190MJ8	LT1202CS	LT1214CN	LT1223CS8

# Multisim 14.0 Education Components

---

LT1223MJ8	LT1253CS8	LT1358CN8	LT1395CS6
LT1224CN8	LT1254CN	LT1358CS8	LT1395CS8
LT1224CS8	LT1254CS	LT1359CN	LT1396CDD
LT1225CN8	LT1256CN	LT1359CS	LT1396CMS8
LT1225CS8	LT1256CS	LT1359CS14	LT1396CS8
LT1226CN8	LT1259CN	LT1360CN8	LT1397CGN
LT1226CS8	LT1259CS	LT1360CS8	LT1397CS
LT1227CN8	LT1260CN	LT1361CN8	LT1398CS
LT1227CS8	LT1260CS	LT1361CS8	LT1399CGN
LT1227MJ8	LT1328CMS8	LT1362CN	LT1399CS
LT1228CN8	LT1328CS8	LT1362CS	LT1413ACN8
LT1228CS8	LT1351CMS8	LT1363CN8	LT1413CN8
LT1229CJ8	LT1351CN8	LT1363CS8	LT1413S8
LT1229CN8	LT1351CS8	LT1364CN8	LT1431CN8
LT1229CS8	LT1352CN8	LT1364CS8	LT1431CS8
LT1229MJ8	LT1352CS8	LT1365CN	LT1457CN8
LT1230CJ	LT1353CS	LT1365CS	LT1457S8
LT1230CN	LT1354CN8	LT1366CN8	LT1461-25
LT1230CS	LT1354CS8	LT1366CS8	LT1461-3
LT1230MJ	LT1355CN8	LT1367CS	LT1461-33
LT1251CN	LT1355CS8	LT1368CN8	LT1461-4
LT1251CS	LT1356CN	LT1368CS8	LT1461-5
LT1252CN8	LT1356CS	LT1369CS	LT1462CN8
LT1252CS8	LT1357CN8	LT1394CMS8	LT1462CS8
LT1253CN8	LT1357CS8	LT1395CS5	LT1463CN

# Multisim 14.0 Education Components

---

LT1463CS	LT1494CN8	LT1636CDD	LT1673IS8
LT1464CN8	LT1494CS8	LT1636CMS8	LT1674CN
LT1464CS8	LT1495CN8	LT1636CN8	LT1674CS
LT1465CN	LT1495CS8	LT1636CS8	LT1674IN
LT1465CS	LT1496CN	LT1637CDD	LT1674IS
LT1466LCN8	LT1496CS	LT1637CMS8	LT1677CN8
LT1466LCS8	LT1497CS	LT1637CN8	LT1677CS8
LT1467LCS	LT1497CS8	LT1637CS8	LT1678CS8
LT1468CDD	LT1498CN8	LT1638CDD	LT1679CS
LT1468CN8	LT1498CS8	LT1638CMS8	LT1711CMS8
LT1468CS8	LT1499CS	LT1638CN8	LT1712CGN
LT1468IDD	LT1521CMS8	LT1638CS8	LT1713CMS8
LT1468IN8	LT1521CS8	LT1639CN	LT1714CGN
LT1468IS8	LT1529CQ	LT1639CS	LT1715CMS
LT1469CN8	LT1529CT	LT1671CMS8	LT1716CS5
LT1469CS8	LT1568CGN	LT1671CS8	LT1719CS8
LT1490CMS8	LT1568IGN	LT1672CMS8	LT1719IS8
LT1490CN8	LT1630CN8	LT1672CN8	LT1720CDD
LT1490CS8	LT1630CS8	LT1672CS8	LT1720CMS8
LT1491CN	LT1631CS	LT1672IMS8	LT1720CS8
LT1491CS	LT1632CN8	LT1672IN8	LT1720IDD
LT1492CN8	LT1632CS8	LT1672IS8	LT1720IMS8
LT1492CS8	LT1633CS	LT1673CN8	LT1720IS8
LT1493CS	LT1635CN8	LT1673CS8	LT1721CGN
LT1494CMS8	LT1635CS8	LT1673IN8	LT1721CS

# Multisim 14.0 Education Components

---

LT1721IGN	LT1763CDE-1.8	LT1782CS6	LT1801CDD
LT1722CS5	LT1763CDE-2.5	LT1783CS6	LT1801CMS8
LT1722CS8	LT1763CDE-3	LT1784CS6	LT1801CS8
LT1723CMS8	LT1763CDE-3.3	LT1784IS6	LT1802CS
LT1723CS8	LT1763CDE-5	LT1787CMS8	LT1806CS6
LT1724CS	LT1763CS8	LT1789CS8-1	LT1806CS8
LT1739CFE	LT1763CS8-1.5	LT1789CS8-10	LT1807CMS8
LT1739CUE	LT1763CS8-1.8	LT1790ACS6-1.25	LT1807CS8
LT1739IFE	LT1763CS8-2.5	LT1790ACS6-2.048	LT1809CS6
LT1739IUE	LT1763CS8-3	LT1790ACS6-2.5	LT1809CS8
LT1761ES5-1.8	LT1763CS8-3.3	LT1790ACS6-3	LT1810CMS8
LT1761ES5-2	LT1763CS8-5	LT1790ACS6-3.3	LT1810CS8
LT1761ES5-2.5	LT1763IS8	LT1790ACS6-4.096	LT1812CS5
LT1761ES5-3	LT1763IS8-1.5	LT1790ACS6-5	LT1812CS6
LT1761ES5-3.3	LT1763IS8-1.8	LT1792CN8	LT1812CS8
LT1761ES5-5	LT1764EFE	LT1792CS8	LT1813CDD
LT1761ES5-BYP	LT1764EFE-1.5	LT1793CN8	LT1813CS8
LT1761ES5-SD	LT1764EFE-1.8	LT1793CS8	LT1813DMS8
LT1762EMS8	LT1764EFE-2.5	LT1794CFE	LT1814CGN
LT1762EMS8-2.5	LT1764EFE-3.3	LT1794CSW	LT1814CS
LT1762EMS8-3	LT1764EQ	LT1795CFE	LT1815CS5
LT1762EMS8-3.3	LT1764EQ-1.5	LT1795CSW	LT1815CS6
LT1762EMS8-5	LT1764EQ-1.8	LT1797CS5	LT1815CS8
LT1763CDE	LT1764EQ-2.5	LT1800CS5	LT1815IS5
LT1763CDE-1.5	LT1764EQ-3.3	LT1800CS8	LT1815IS6

# Multisim 14.0 Education Components

---

LT1815IS8	LT1884CN8	LT1994CDD	LT6001IMS8
LT1816ACMS	LT1884CS8	LT1994CMS8	LT6002CDHC
LT1816AIMS	LT1885CS	LT1995CDD	LT6002CGN
LT1816CDD	LT1886CS8	LT1995CMS	LT6002IDHC
LT1816CMS8	LT1920CN8	LT1995IDD	LT6002IGN
LT1816CS8	LT1920CS8	LT1995IMS	LT6003CDC
LT1816IDD	LT1962EMS8	LT1996CDD	LT6003CS5
LT1816IMS8	LT1962EMS8-1.5	LT1996CMS	LT6003HDC
LT1816IS8	LT1962EMS8-1.8	LT2078ACS8	LT6003HS5
LT1817CGN	LT1962EMS8-2.5	LT2078AIS8	LT6003IDC
LT1817CS	LT1962EMS8-3	LT2078CS8	LT6003IS5
LT1817IGN	LT1962EMS8-3.3	LT2079ACS	LT6004CDD
LT1817IS	LT1962EMS8-5	LT2079CS	LT6004CMS8
LT1818CS5	LT1963EFE	LT2178ACS8	LT6004HDD
LT1818CS8	LT1963EFE-1.5	LT2178CS8	LT6004HMS8
LT1818IS5	LT1963EFE-1.8	LT2179ACS	LT6004IDD
LT1818IS8	LT1963EFE-2.5	LT2179CS	LT6004IMS8
LT1819CMS8	LT1963EFE-3.3	LT318A	LT6005CDHC
LT1819CS8	LT1970CFE	LT318AJ8	LT6005CGN
LT1819IMS8	LT1990CS8	LT318AN8	LT6005HDHC
LT1819IS8	LT1991CDD	LT6000CDCB	LT6005HGN
LT1880CS5	LT1991CMS	LT6000IDCB	LT6005IDHC
LT1881CN8	LT1993CUD-10	LT6001CDD	LT6005IGN
LT1881CS8	LT1993CUD-2	LT6001CMS8	LT6010CDD
LT1882CS	LT1993CUD-4	LT6001IDD	LT6010CS8

# Multisim 14.0 Education Components

---

LT6011CDD	LT6220CS5	LT6552IS8	LTC1047CN8
LT6011CMS8	LT6220CS8	LT6553CGN	LTC1047CS
LT6011CS8	LT6221CDD	LT6553IGN	LTC1049CJ8
LT6012CGN	LT6221CS8	LT6557CDHC	LTC1049CN8
LT6012CS	LT6222CGN	LT6557CGN	LTC1049CS8
LT6100CDD	LT6230CS6	LT6557IDHC	LTC1050ACH
LT6100CMS8	LT6231CDD	LT6557IGN	LTC1050ACJ8
LT6200CS6	LT6231CS8	LT6558CDHC	LTC1050ACN
LT6200CS6-10	LT6232CGN	LT6558CGN	LTC1050ACN8
LT6200CS6-5	LT6233CS6	LT6558IDHC	LTC1050AMH
LT6200CS8	LT6234CDD	LT6558IGN	LTC1050AMJ8
LT6200CS8-10	LT6234CS8	LT6559CUD	LTC1050CH
LT6200CS8-5	LT6235CGN	LT6600-10	LTC1050CJ8
LT6201CDD	LT6235IGN	LT6600-2.5	LTC1050CN
LT6201CS8	LT6402CUD-12	LT6600-20	LTC1050CN8
LT6202CS5	LT6402CUD-20	LT6600-5	LTC1050MH
LT6202CS8	LT6402CUD-6	LT6650CS5	LTC1050MJ8
LT6203CDD	LT6402IUD-12	LT6700CDCB-1	LTC1051ACJ8
LT6203CMS8	LT6402IUD-20	LT6700CDCB-2	LTC1051ACN8
LT6203CS8	LT6402IUD-6	LT6700CDCB-3	LTC1051ACS
LT6204CGN	LT6411CUD	LT6700CS6-1	LTC1051AMJ8
LT6204CS	LT6411IUD	LT6700CS6-2	LTC1051CJ8
LT6205CS5	LT6552CDD	LT6700CS6-3	LTC1051CN8
LT6206CMS8	LT6552CS8	LTC1043CN	LTC1051CS
LT6207CGN	LT6552IDD	LTC1043CSW	LTC1051MJ8



# Multisim 14.0 Education Components

---

LTC1052CD	LTC1441CS8	LTC1563-2CGN	LTC2055CMS8
LTC1052CP	LTC1442CN8	LTC1563-3CGN	LTC6078CDD
LTC1052CS	LTC1442CS8	LTC1798CS8	LTC6078CMS8
LTC1052MD	LTC1443CDHD	LTC1798CS8-2.5	LTC6079CDHC
LTC1052MP	LTC1443CN	LTC1798CS8-3	LTC6079CGN
LTC1053CN	LTC1443CS	LTC1798CS8-4.1	LTC6101ACMS8
LTC1053CS	LTC1444CDHD	LTC1798CS8-5	LTC6101BCS5
LTC1053CSW	LTC1444CN	LTC1841CS8	LTC6240CS5
LTC1100CN8	LTC1444CS	LTC1842CS8	LTC6240CS8
LTC1100CSW	LTC1444IDHD	LTC1966CMS8	LTC6240HS5
LTC1150CJ8	LTC1444IN	LTC1967CMS8	LTC6240HS8
LTC1150CN8	LTC1444IS	LTC1968CMS8	LTC6240IS5
LTC1150CS8	LTC1445CDHD	LTC2050CS5	LTC6240IS8
LTC1150MJ8	LTC1445CN	LTC2050CS6	LTC6241CDD
LTC1151CN8	LTC1445CS	LTC2050CS8	LTC6241CS8
LTC1151CSW	LTC152	LTC2051CMS10	LTC6241HS8
LTC1152CN8	LTC1540CDD	LTC2052CGN	LTC6241IDD
LTC1152CS8	LTC1540CMS8	LTC2052CS	LTC6241IS8
LTC1250CN8	LTC1540CS8	LTC2053CDD	LTC6242CDHC
LTC1250CS8	LTC1541CDD	LTC2053CMS8	LTC6242CGN
LTC1440CDD	LTC1541CMS8	LTC2053HDD	LTC6242HGN
LTC1440CMS8	LTC1541CS8	LTC2053HMS8	LTC6242IDHC
LTC1440CN8	LTC1542CDD	LTC2053IMS8-SYNC	LTC6242IGN
LTC1440CS8	LTC1542CMS8	LTC2054CS5	LTC6244CDD
LTC1441CN8	LTC1542CS8	LTC2055CDD	LTC6244CMS8

# Multisim 14.0 Education Components

---

LTC6244HMS8	MAC15A-8	MAC224-4	MAT03EH
LTC6244IDD	MAC210-10	MAC224-6	MAT03FH
LTC6244IMS8	MAC210-4	MAC224-8	MAT04AY
LTC6800HDD	MAC210-6	MAC224A-10	MAT04EY
LTC6800HMS8	MAC210-8	MAC224A-4	MAT04FP
LTC6910-1CTS8	MAC210A-10	MAC224A-6	MAT04FS
LTC6910-2CTS8	MAC210A-4	MAC224A-8	MAT04FY
LTC6910-3CTS8	MAC210A-6	MAC228-10	MAX1180_FP48
LTC6911CMS-1	MAC210A-8	MAC228-4	MAX1181_FP48
LTC6911CMS-2	MAC212-10	MAC228-6	MAX1182_FP48
LTC7652CH	MAC212-4	MAC228-8	MAX1183_FP48
LTR-516AD	MAC212-6	MAC228A-10	MAX1184_FP48
LVL_BARGRAPH	MAC212-8	MAC228A-4	MAX1185_FP48
LVM_CURRENT	MAC212A-10	MAC228A-6	MAX1195_FP48
LVM_VOLTAGE	MAC212A-4	MAC228A-8	MAX1197_FP48
M6060P-E3/45	MAC212A-6	MAC23A-10	MAX1198_FP48
MAC08MT1G	MAC212A-8	MAG_CMP4	MAX1284_SO8
MAC12HCDG	MAC223-10	MAG_OL	MAX1285_SO8
MAC15-10	MAC223-4	MAG_OL_RELAY	MAX1290_SO28
MAC15-4	MAC223-6	MAGNETIC_CORE_	MAX1291_SO28
MAC15-6	MAC223-8	VIRTUAL	MAX1292_SO24
MAC15-8	MAC223A-4	MAGNETIC_FLUX	MAX1293_SO24
MAC15A-10	MAC223A-6	MAGNETIC_FLUX_G	MAX1420_FP48
MAC15A-4	MAC223A-8	ENERATOR	
MAC15A-6	MAC224-10	MAT02EH	MAX1421_FP48
		MAT02FH	MAX1422_FP48

# Multisim 14.0 Education Components

---

MAX1444_FP32	MAX16010TAC+	MAX203EEPP	MAX208CAG
MAX1446_FP32	MAX1666VEEP	MAX203EEWP	MAX208E
MAX1449_FP32	MAX200CPP	MAX203EPP	MAX208EAG
MAX14802ECM+	MAX200ECWP	MAX203EWP	MAX208ECAG
MAX14803AEWZ+	MAX200EEWP	MAX204CPE	MAX208ECWG
MAX14803CCM+	MAX200EPP	MAX204CWE	MAX208EEAG
MAX15000AEUB+	MAX201CPD	MAX204EPE	MAX208EEWG
MAX15000BEUB+	MAX201CWE	MAX204EWE	MAX209
MAX15001AEUB+	MAX201EPD	MAX205CPG	MAX209ENG
MAX15001BEUB+	MAX201EWE	MAX205E	MAX211
MAX15004AAUE+	MAX202CPE	MAX205ECAG	MAX211CAI
MAX15004BAUE+	MAX202CSE	MAX205ECWG	MAX211E
MAX15005AAUE+	MAX202CWE	MAX205EEAG	MAX211EAI
MAX15005BAUE+	MAX202ECPE	MAX205EEWG	MAX211ECAI
MAX15006AASA+	MAX202ECUE	MAX206	MAX211ECWI
MAX15006AATT+	MAX202EEPE	MAX206CAG	MAX211EEAI
MAX15007AASA+	MAX202EEUE	MAX206E	MAX211EEWI
MAX15007AATT+	MAX202ESE	MAX206EAG	MAX213
MAX15024AATB+	MAX202EWE	MAX207	MAX213CAI
MAX15024BATB+	MAX202SE	MAX207CAG	MAX213E
MAX15024CATB+	MAX203CPP	MAX207E	MAX213EAI
MAX15024DATB+T	MAX203CWP	MAX207EAG	MAX213ECAI
MAX15025CATB+T	MAX203E	MAX207ECAG	MAX213ECWI
MAX16010TAA+	MAX203ECPP	MAX207EEAG	MAX213EEAI
MAX16010TAB+	MAX203ECWP	MAX208	MAX213EEWI

# Multisim 14.0 Education Components

---

MAX218	MAX2740ECM	MAX319MJA	MAX3232
MAX218CAP	MAX274ACNG	MAX3212	MAX3232E
MAX218CPP	MAX274ACWI	MAX3212CAI	MAX3237
MAX218EAP	MAX274BCNG	MAX3212EAI	MAX3237E
MAX218EPP	MAX274BCWI	MAX3218	MAX3238E
MAX221ECAE	MAX317CJA	MAX3218CAP	MAX3241
MAX221ECUE	MAX317CPA+	MAX3218CPP	MAX3241E
MAX221EEAE	MAX317CSA+	MAX3218EAP	MAX3243
MAX221EEUE	MAX317EJA	MAX3218EPP	MAX3243E
MAX232E	MAX317EPA+	MAX3221	MAX3243ECAI
MAX232ECPE	MAX317ESA+	MAX3221CAE	MAX3243ECAP
MAX232EEPE	MAX317MJA	MAX3221E	MAX3243ECPP
MAX241E	MAX318CJA	MAX3221EAE	MAX3243EEAI
MAX241ECAI	MAX318CPA+	MAX3221ECAE	MAX3248E
MAX241ECWI	MAX318CSA+	MAX3221EEAE	MAX3380E
MAX241EEAI	MAX318EJA	MAX3222	MAX3381E
MAX241EEWI	MAX318EPA	MAX3222E	MAX4004EUT+
MAX253CPA+	MAX318ESA+	MAX3223	MAX4006EUT+
MAX253CSA+	MAX318MJA	MAX3223E	MAX4007EUT+
MAX253CUA+	MAX319CJA	MAX3223ECAP	MAX4008EUT+
MAX253EPA+	MAX319CPA+	MAX3223ECPP	MAX4012ESA+
MAX253ESA+	MAX319CSA+	MAX3223ECUP	MAX4012EUK+
MAX253EUA+	MAX319EJA	MAX3223EEAP	MAX4016ESA+
MAX253MJA	MAX319EPA+	MAX3223EEPP	MAX4016EUA+
MAX253MSA/PR	MAX319ESA+	MAX3223EEUP	MAX4018EEE+

# Multisim 14.0 Education Components

---

MAX4018ESD+	MAX4038EUA+	MAX4073TAUT+	MAX409ACPA+
MAX4020EEE+	MAX4039EBL+T	MAX4073TAXK+	MAX409ACSA+
MAX4020ESD+	MAX4039ETB+T	MAX407CPA+	MAX409AEPA
MAX4023EEE+	MAX4039EUB+	MAX407CSA+	MAX409AESA+
MAX4023ESE+	MAX403CPA	MAX407EPA+	MAX409AMJA
MAX4024ESD+	MAX403CSA	MAX407ESA+	MAX409BCPA+
MAX4024EUD+	MAX403EPA	MAX407MJA	MAX409BCSA+
MAX4027ESD+	MAX403ESA	MAX4080FASA+	MAX409BEPA+
MAX4027EUD+	MAX4069AUB+	MAX4080FAUA+	MAX409BESA+
MAX4028EUE+	MAX406ACPA+	MAX4080SASA+	MAX4100ESA
MAX4028EWE+	MAX406ACSA+	MAX4080SAUA+	MAX4100ESA+
MAX4029EUP+	MAX406AEPA+	MAX4080TASA+	MAX4100EUA+
MAX4029EWP+	MAX406AESA+	MAX4080TAUA+	MAX4101ESA
MAX402CPA	MAX406AMJA	MAX4081FASA+	MAX4101ESA+
MAX402CSA	MAX406BCPA+	MAX4081FAUA+	MAX4104ESA
MAX402EPA	MAX406BCSA+	MAX4081SASA+	MAX4104ESA+
MAX402ESA	MAX406BEPA+	MAX4081SAUA+	MAX4104EUK+
MAX4032EUT+	MAX406BESA+	MAX4081TASA+	MAX4105ESA+
MAX4032EXT+	MAX406BMJA	MAX4081TAUA+	MAX4105EUK+T
MAX4036AAXK+	MAX4070ATA+	MAX4090AALT+T	MAX4106ESA
MAX4036EXK+	MAX4070AUA+	MAX4090AAUT+	MAX4106ESA+
MAX4037EUT+	MAX4071ATA+	MAX4090AAXT+	MAX4107ESA
MAX4038AAUA+	MAX4071AUA+	MAX4090ELT+T	MAX4107ESA+
MAX4038EBL+T	MAX4072ATA+	MAX4090EUT+	MAX4108ESA
MAX4038ETA+	MAX4072AUA+	MAX4090EXT+	MAX4108ESA+

# Multisim 14.0 Education Components

---

MAX4109ESA+	MAX4126EUA+	MAX4132ESA+	MAX414ESD+
MAX410BCPA	MAX4128ESA+	MAX4132EUA+	MAX414MJD
MAX410BCSA	MAX4128EUA+	MAX4133ESD	MAX4162ESA+
MAX410BCSA+	MAX4129ESD+	MAX4134ESD+	MAX4162EUK+
MAX410BEPA	MAX412BCPA	MAX4144EEE+	MAX4163EBL+
MAX410BESA	MAX412BCPA+	MAX4144ESD+	MAX4163ESA+
MAX410CPA	MAX412BCSA	MAX4145EEE+	MAX4163EUA+
MAX410CPA+	MAX412BCSA+	MAX4145ESD+	MAX4164ESD+
MAX410CSA	MAX412BEPA	MAX4146EEE+	MAX4165EUK+
MAX410CSA+	MAX412BEPA+	MAX4146ESD+	MAX4166ELA+
MAX410EPA	MAX412BESA	MAX4147ESD	MAX4166EPA+
MAX410EPA+	MAX412BESA+	MAX4147ESD+	MAX4166ESA+
MAX410ESA+	MAX412CPA	MAX414BCPD	MAX4166EUA+
MAX410ETA-T	MAX412CPA+	MAX414BCSD	MAX4167EPA+
MAX4112ESA+	MAX412CSA	MAX414BCSD+	MAX4167ESA+
MAX4112EUA	MAX412CSA+	MAX414BEPD	MAX4168EPD+
MAX4113ESA+	MAX412EPA	MAX414BESD	MAX4168ESD+
MAX4117ESA+	MAX412EPA+	MAX414BESD+	MAX4168EUB+
MAX4118ESA+	MAX412ESA	MAX414CPD	MAX4169EPD
MAX4119EEE	MAX412ESA+	MAX414CPD+	MAX4169ESD+
MAX4119ESD+	MAX412MJA	MAX414CSD	MAX4172EUA+
MAX4120ESD+	MAX4130EUK+	MAX414CSD+	MAX4173TESA+
MAX4122EUK+	MAX4131EBT+	MAX414EPD	MAX4173TEUT+
MAX4124EUK+	MAX4131ESA+	MAX414EPD+	MAX4178EPA+
MAX4126ESA+	MAX4131EUA+	MAX414ESD	MAX4178ESA+

# Multisim 14.0 Education Components

---

MAX4178EUA+	MAX418CPD+	MAX4202EUK+T	MAX4222ESD+
MAX4178EUK+T	MAX418CSD+	MAX4203ESA+	MAX4223ESA+
MAX4178MJA	MAX418EPD+	MAX4203EUA+	MAX4223EUT+
MAX417CPA+	MAX418ESD+	MAX4204ESA+	MAX4224ESA+
MAX417CSA+	MAX418MJD	MAX4204EUA+	MAX4224EUT+
MAX417EPA+	MAX4190ESA+	MAX4205ESA	MAX4225ESA+
MAX417ESA+	MAX4190EUA	MAX4205EUA+	MAX4226ESD
MAX417MJA	MAX4194ESA+	MAX4206ETE	MAX4226EUB+
MAX4180ESA+	MAX4195ESA+	MAX4212EUK+	MAX4227ESA+
MAX4180EUT+T	MAX4196ESA+	MAX4213ESA+	MAX4228ESD+
MAX4181ESA+	MAX4197ESA+	MAX4213EUA+	MAX4228EUB+
MAX4181EUT+T	MAX4198ESA+	MAX4214EUK+	MAX4230AUK+
MAX4182ESA+	MAX4198EUA+	MAX4215ESA+	MAX4230AXK+
MAX4183ESD+	MAX4199ESA+	MAX4215EUA+	MAX4231ART+T
MAX4183EUB+	MAX4199EUA+	MAX4216ESA+	MAX4231AUT+
MAX4184ESA+	MAX419CPD+	MAX4216EUA+	MAX4231AXT+
MAX4185ESD	MAX419CSD+	MAX4217ESA+	MAX4231AYT+
MAX4185EUB+	MAX419EPD+	MAX4217EUA+	MAX4232AKA+
MAX4186ESD+	MAX419ESD+	MAX4218EEE+	MAX4232AUA+
MAX4187EEE+	MAX419MJD	MAX4218ESD+	MAX4233ABC+T
MAX4187ESD+	MAX4200ESA+	MAX4219EEE+	MAX4233AUB+
MAX4188EEE+	MAX4200EUK+	MAX4219ESD+	MAX4234ASD+
MAX4188ESD+	MAX4201ESA+	MAX4220EEE+	MAX4234AUD+
MAX4189EEE+	MAX4201EUK+T	MAX4220ESD+	MAX4236AESA+
MAX4189ESD+	MAX4202ESA+	MAX4222EEE+	MAX4236AEUA

# Multisim 14.0 Education Components

---

MAX4236BESA+	MAX4249ESD+	MAX4268ESD+	MAX4288ESD
MAX4236BEUA+	MAX4249EUB+	MAX4269EEE	MAX4288EUB
MAX4236EUT+	MAX4250AAUK+	MAX4269ESD	MAX4289ESA+
MAX4237AESA+	MAX4250EUK+	MAX4270EEE	MAX4289EUT+
MAX4237AEUA+	MAX4251ESA+	MAX4270ESD	MAX4291EUK+
MAX4237BESA+	MAX4251EUA+	MAX4278EPA+	MAX4291EXK+
MAX4237BEUA+	MAX4252EBL+	MAX4278ESA+	MAX4292EBL+
MAX4237EUT+	MAX4252ESA+	MAX4278EUA+	MAX4292ESA+
MAX4238ASA+	MAX4252EUA+	MAX4278EUK+	MAX4292EUA+
MAX4238ATT+	MAX4253EBC+	MAX4278MJA	MAX4294ESD+
MAX4238AUT+	MAX4253ESD+	MAX427CPA+	MAX4294EUD+
MAX4239ASA+	MAX4253EUB+	MAX427CSA+	MAX4304ESA+
MAX4239ATT+	MAX4254ESD+	MAX427EPA+	MAX4304EUK+
MAX4239AUT+	MAX4255EUK+	MAX427ESA+	MAX4305ESA+
MAX4240EUK+	MAX4256ESA+	MAX427MJA	MAX4305EUK+
MAX4241ESA+	MAX4256EUA+	MAX4281ESA+	MAX4323EBT+T
MAX4241EUA+	MAX4257ESA+	MAX4281EUK+	MAX4323ESA+
MAX4242ESA+	MAX4257EUA+	MAX4282ESA+	MAX4323EUA
MAX4242EUA+	MAX4265ESA+	MAX4282EUA+	MAX4323EUT+
MAX4243ESD	MAX4265EUA+	MAX4284EEE	MAX4327ESD
MAX4243EUB+	MAX4266ESA+	MAX4284ESD	MAX4327EUB+
MAX4244ESD+	MAX4266EUA+	MAX4285ESA+	MAX4330EUK+
MAX4245AUT+	MAX4267ESA+	MAX4285EUT+	MAX4331ESA+
MAX4245AXT+	MAX4267EUA	MAX4286ESA+	MAX4331EUA+
MAX4247AUB+	MAX4268EEE+	MAX4286EUT-T	MAX4332ESA+



# Multisim 14.0 Education Components

---

MAX4333ESD+	MAX436EPD	MAX4375FESD+	MAX4388ESD+
MAX4333EUB+	MAX436ESD	MAX4375FEUB+	MAX4388EUB
MAX4334ESD+	MAX436ESD+	MAX4375HESD+	MAX4389EUT+
MAX4335EXT+	MAX436MJD	MAX4375HEUB+	MAX4389EXT+
MAX4336EUT-T	MAX4372FEBT+T	MAX4375TESD+	MAX4390EUK+
MAX4336EXT+	MAX4372FESA+	MAX4375TEUB+	MAX4390EXT+
MAX4337EKA+	MAX4372FEUK+	MAX437CPA	MAX4392ESA+
MAX4337EUA+	MAX4372HEBT+T	MAX437CSA+	MAX4392EUA+
MAX4338EUB+	MAX4372HESA+	MAX437EPA	MAX4393EUB+
MAX435CPD	MAX4372HEUK+	MAX437ESA+	MAX4394ESD+
MAX435CSD	MAX4372TEBT+T	MAX437MJA	MAX4394EUD+
MAX435CSD+	MAX4372TESA+	MAX4380EUT+	MAX4395ESD+
MAX435EPD	MAX4372TEUK+	MAX4380EXT+	MAX4395EUD+
MAX435ESD	MAX4373FESA+	MAX4381EUB+	MAX4396EUP+
MAX435ESD+	MAX4373FEUA+	MAX4382EEE+	MAX4400AUK+
MAX435MJD	MAX4373HESA+	MAX4382ESD+	MAX4400AXK+
MAX4361	MAX4373HEUA+	MAX4382EUD+	MAX4401AXT+
MAX4361ESA	MAX4373TESA+	MAX4383EEE+	MAX4402AKA+
MAX4361EUA	MAX4373TEUA+	MAX4383ESD+	MAX4402ASA+
MAX4362ESD+	MAX4374FESD+	MAX4383ESE+	MAX4402AUA+
MAX4362EUB+	MAX4374FEUB+	MAX4383EUD+	MAX4403ASD+
MAX4363EUP+	MAX4374HESD+	MAX4384EUP+	MAX4403AUD+
MAX436CPD	MAX4374HEUB+	MAX4385EEUK+	MAX4412EUK+
MAX436CSD	MAX4374TESD+	MAX4386EESD+	MAX4412EXK+
MAX436CSD+	MAX4374TEUB+	MAX4386EEUD+	MAX4413EKA+

# Multisim 14.0 Education Components

---

MAX4414ESA+	MAX44285FAUA+	MAX4452EUK+	MAX4462UETT+
MAX4414EUA+	MAX44285FAWA+T	MAX4452EXK+	MAX4464EUK+
MAX4415ESA+	MAX44285HAUA+	MAX4453EKA+	MAX4464EXK+
MAX4415EUA+	MAX44285HAWA+T	MAX4453ESA+	MAX4473ESA
MAX4416ESA+	MAX44285LAUA+	MAX4454ESD+	MAX4473EUA+
MAX4416EUA+	MAX44285LAWA+T	MAX4454EUD+	MAX4474EKA+
MAX4417ESA+	MAX44285TAUA+	MAX4460ESA+	MAX4474ESA+
MAX4417EUA+	MAX44285TAWA+T	MAX4460ETT+	MAX4474EUA+
MAX4418EUD+	MAX4430ESA+	MAX4460EUT+T	MAX4475ASA+
MAX4419EUD+	MAX4430EUK+	MAX4461HESA+	MAX4475ATT+
MAX44241AUA+	MAX4432ESA	MAX4461HETT+T	MAX4475AUA+
MAX44241AUK+T	MAX4432EUA+	MAX4461HEUT+	MAX4475AUT+
MAX44243ASD+	MAX4434ESA	MAX4461TESA+	MAX4476ATT+T
MAX44243AUD+	MAX4434EUK+	MAX4461TETT+	MAX4476AUT+
MAX44251AKA+	MAX4435ESA	MAX4461TEUT	MAX4477ASA+
MAX44251AUA+	MAX4435EUK	MAX4461UESA+	MAX4477AUA+
MAX44252ASD+	MAX4436ESA	MAX4461UETT+T	MAX4478ASD+
MAX44264EWT+	MAX4436EUA+	MAX4461UEUT-T	MAX4478AUD+
MAX44265EWT+	MAX4437ESA	MAX4462HESA+	MAX4480AUK+
MAX44269EWL+	MAX4437EUA+	MAX4462HETT+	MAX4480AXK+
MAX44280AXT+	MAX4444ESE+	MAX4462HEUT+	MAX4481AUT+
MAX44280AYT+	MAX4450EUK+	MAX4462TESA	MAX4481AXT+
MAX44281OANS+	MAX4450EXK+	MAX4462TETT+T	MAX4482AKA+
MAX44281UANS+	MAX4451EKA+	MAX4462TEUT	MAX4482ASA+
MAX44281VANS+	MAX4451ESA+	MAX4462UESA	MAX4482AUA+

# Multisim 14.0 Education Components

---

MAX4483ASD+	MAX4494AUA+	MAX4601CAE+	MAX4667ESE+
MAX4483AUD+	MAX4495ASD+	MAX4601CPE+	MAX4668CPE+
MAX4484AUK+	MAX4495AUD+	MAX4601CWE+	MAX4668CSE+
MAX4484AXK+	MAX4541CPA+	MAX4601EAE+	MAX4668EPE+
MAX4486AKA+	MAX4541CSA+	MAX4601EPE+	MAX4668ESE+
MAX4486ASA+	MAX4541CUA+	MAX4601EWE	MAX4669CPE
MAX4486AUA+	MAX4541EKA+	MAX4602CAE+	MAX4669CSE+
MAX4487ASD+	MAX4541EPA	MAX4602CPE+	MAX4669EPE
MAX4487AUD+	MAX4541ESA+	MAX4602CWE+	MAX4669ESE+
MAX4488ASA+	MAX4541ETA+T	MAX4602EAE+	MAX4670ETJ+
MAX4488ATT+	MAX4541EUA	MAX4602EPE	MAX4684EBC+
MAX4488AUA+	MAX4541EUA+	MAX4602EWE+	MAX4684ETB+
MAX4488AUT+	MAX4542CSA+	MAX4603CAE+	MAX4684EUB+
MAX4489ASA+	MAX4542CUA	MAX4603CPE+	MAX4685EBC+T
MAX4489AUA+	MAX4542EKA+	MAX4603CWE+	MAX4685ETB+T
MAX4490AUK+T	MAX4542EPA	MAX4603EAE+	MAX4685EUB+
MAX4490AXK+	MAX4542ESA+	MAX4603EPE+	MAX4714ELT+
MAX4491AKA+	MAX4542EUA+	MAX4603EWE+	MAX4714EXT+
MAX4491AUA+	MAX4543CPA	MAX4659ESA+	MAX4717EBC+
MAX4492ASD+	MAX4543CSA	MAX4659EUA+	MAX4717ETB+
MAX4492AUD+	MAX4543CUA	MAX4660ESA+	MAX4717EUB+
MAX4493AUK	MAX4543EKA+	MAX4660EUA+	MAX4718EBC-T
MAX4493AXK+	MAX4543EPA	MAX4667CPE	MAX4718EUB
MAX4494AKA+	MAX4543ESA+	MAX4667CSE	MAX4719EBC-T
MAX4494ASA+	MAX4543EUA+	MAX4667EPE	MAX4719EUB+

# Multisim 14.0 Education Components

---

MAX473CPA	MAX475ESD	MAX4885ETJ+	MAX495CPA
MAX473CPA+	MAX475MJD	MAX4887ETE+	MAX495CPA+
MAX473CSA	MAX477EPA+	MAX4889AETO+	MAX495CSA
MAX473CSA+	MAX477ESA+	MAX4890ETJ+	MAX495CSA+
MAX473CUA	MAX477EUA+	MAX4891ETJ+	MAX495CUA
MAX473CUA+	MAX477EUK+T	MAX4892ETX+	MAX495CUA+
MAX473EPA+	MAX477MJA	MAX4906FELB+	MAX495EPA+
MAX473ESA+	MAX478ACPA+	MAX4906FETB+T	MAX495ESA+
MAX473MJA	MAX478CPA+	MAX4907FELA+	MAX495MJA
MAX474CPA	MAX478CSA+	MAX4907FETA+T	MAX496CPE+
MAX474CPA+	MAX478EPA+	MAX492CPA	MAX496CSE+
MAX474CSA	MAX478ESA+	MAX492CPA+	MAX497CPE+
MAX474CSA+	MAX479ACPD	MAX492CSA	MAX497CSE+
MAX474CUA	MAX479CPD+	MAX492CSA+	MAX5025EUT+
MAX474CUA+	MAX479CSD+	MAX492EPA+	MAX5027EUT+
MAX474EPA+	MAX479EPD+	MAX492ESA+	MAX5035AASA+
MAX474ESA+	MAX479ESD+	MAX492MJA	MAX5035AUPA+
MAX474MJA	MAX4800CCM+	MAX494CPD	MAX5035AUSA+
MAX4754AEBE+T	MAX4800CQI+	MAX494CPD+	MAX5035BASA+
MAX4754AETE+	MAX4800CTM+	MAX494CSD	MAX5035BUPA+
MAX4754EBE+T	MAX4800CXZ+	MAX494CSD+	MAX5035BUSA+
MAX4754ETE+	MAX4801CQI+	MAX494EPD+	MAX5035CASA+
MAX475CPD	MAX4818ETE+	MAX494ESD+	MAX5035CUPA+
MAX475CSD	MAX4819ETE	MAX494MJD	MAX5035CUSA+
MAX475EPD	MAX4885EETG+	MAX4951CTP+	MAX5048AATT+

# Multisim 14.0 Education Components

---

MAX5048AAUT+T	MAX5903ACETT+	MAX6324AUT44-T	MAX6324EUT46+T
MAX5054AATA+	MAX5903ACEUT+	MAX6324AUT46+T	MAX6324FUT23+T
MAX5064AATC+	MAX5903LAETT+T	MAX6324BUT23+T	MAX6324FUT26+T
MAX5078AATT+	MAX5903LAEUT+	MAX6324BUT26-T	MAX6324FUT29-T
MAX5078BATT+	MAX5903LBETT+	MAX6324BUT29+T	MAX6324FUT31-T
MAX5631_QFN68	MAX5903LBEUT+	MAX6324BUT31-T	MAX6324FUT44-T
MAX5632_QFN68	MAX5903LCETT+T	MAX6324BUT44-T	MAX6324FUT46+T
MAX5633_QFN68	MAX5903LCEUT+	MAX6324BUT46+T	MAX6324GUT23-T
MAX5902AAETT+	MAX5920AESA+	MAX6324CUT23+T	MAX6324GUT26+T
MAX5902AAEUT+	MAX5920BESA+	MAX6324CUT26+T	MAX6324GUT29+T
MAX5902ABETT+T	MAX5921AESA+	MAX6324CUT29-T	MAX6324GUT31-T
MAX5902ABEUT+	MAX5941ACSE+	MAX6324CUT31-T	MAX6324GUT44-T
MAX5902ABEUT-T	MAX5941AESE+	MAX6324CUT44-T	MAX6324GUT46+T
MAX5902ACETT+T	MAX5941BCSE+	MAX6324CUT46+T	MAX6324HUT23+T
MAX5902ACEUT+	MAX5941BESE+	MAX6324DUT23+T	MAX6324HUT26-T
MAX5902LAETT+	MAX5942ACSE+	MAX6324DUT26+T	MAX6324HUT29+T
MAX5902LAEUT+	MAX5942AESE+	MAX6324DUT29-T	MAX6324HUT31+T
MAX5902LBETT+T	MAX5942BCSE+	MAX6324DUT31-T	MAX6324HUT44+T
MAX5902LBEUT+T	MAX5942BESE+	MAX6324DUT44-T	MAX6324HUT46+T
MAX5902LCETT+T	MAX5949AESA+	MAX6324DUT46-T	MAX6460UT+
MAX5902LCEUT+	MAX5953DUTM+	MAX6324EUT23+T	MAX6780LTA+
MAX5903AAETT+T	MAX6324AUT23-T	MAX6324EUT26+T	MAX6817EUT/GH9-T
MAX5903AAEUT+	MAX6324AUT26-T	MAX6324EUT29+	MAX6817EUT+
MAX5903ABETT+	MAX6324AUT29+T	MAX6324EUT31-T	MAX6817EUT+T
MAX5903ABEUT+	MAX6324AUT31+T	MAX6324EUT44-T	

# Multisim 14.0 Education Components

---

MAX6817EUT-T	MAX809MEUR+	MAX9003ESA+	MAX9077EKA+
MAX6817EUT-TG1K	MAX809MEXR+	MAX9003EUA+	MAX9077ESA+
MAX706RCPA	MAX809REUR+	MAX9005ESA+	MAX9077EUA+
MAX706RCSA+	MAX809REXR+	MAX9005EUA+	MAX9077MSA/PR2
MAX706RCUA+	MAX809SEUR+	MAX9010EXT+	MAX907CPA
MAX706REPA	MAX809SEXR+	MAX9011EUT+	MAX907CPA+
MAX706RESA+	MAX809TEUR+	MAX9012ESA+	MAX907CSA
MAX706REUA+	MAX809TEXR+	MAX9012EUA+	MAX907CSA+
MAX706RMJA	MAX809ZEXR+	MAX9013ESA+	MAX907EPA
MAX706TCPA+	MAX810LEUR+	MAX9013EUA+	MAX907EPA+
MAX706TCSA+	MAX810LEXR+	MAX9015AEKA+	MAX907ESA
MAX706TCUA+	MAX810MEUR+	MAX9026EBT+	MAX907ESA+
MAX706TEPA	MAX810MEXR+	MAX9030AUT+	MAX907MJA
MAX706TESA+	MAX810REUR+	MAX9030AXT+	MAX908CPD
MAX706TEUA+	MAX810REXR+T	MAX9031AUK+	MAX908CPD+
MAX706TMJA	MAX810SEUR+	MAX9031AXK+	MAX908CSD
MAX803LEXR+	MAX810SEXR+	MAX9032AKA+	MAX908CSD+
MAX803MEXR+	MAX810TEUR+	MAX9032ASA+	MAX908EPD
MAX803REXR+	MAX810TEXR+	MAX9032AUA+	MAX908EPD+
MAX803SEXR+	MAX810ZEXR+T	MAX9034ASD+	MAX908ESD
MAX803TEXR+	MAX8815AETB+	MAX9034AUD+	MAX908ESD+
MAX803ZEXR+	MAX9000ESA+	MAX9038BABT+T	MAX908MJD
MAX809JEUR+	MAX9000EUA+	MAX9038BEBT+T	MAX9092AKA+T
MAX809LEUR+	MAX9002ESA+	MAX9075EUK+	MAX9092AUA+
MAX809LEXR+	MAX9002EUA+	MAX9075EXK+	MAX9094ASD+

# Multisim 14.0 Education Components

---

MAX9094AUD+	MAX913EPA+	MAX921CSA+	MAX923EPA+
MAX909CPA	MAX913ESA	MAX921CUA	MAX923ESA
MAX909CSA	MAX913ESA+	MAX921CUA+	MAX923ESA+
MAX909EPA	MAX913EUA+	MAX921EPA	MAX923MJA
MAX909ESA	MAX913MJA	MAX921EPA+	MAX924CPE
MAX909MJA	MAX913MSA/PR	MAX921ESA	MAX924CPE+
MAX9117ESA+	MAX9140AAUK+	MAX921ESA+	MAX924CSE
MAX9117EXK+	MAX9140AAXK+	MAX921MJA	MAX924CSE+
MAX9119EXK+	MAX9140EUK+	MAX922CPA	MAX924EPE
MAX9120ESA	MAX9140EXK+	MAX922CPA+	MAX924EPE+
MAX9120EXK+	MAX9141EKA+	MAX922CSA	MAX924ESE
MAX912CPE	MAX9141ESA+	MAX922CSA+	MAX924ESE+
MAX912CPE+	MAX9142EKA+	MAX922CUA+	MAX924MJE
MAX912CSE	MAX9142ESA+	MAX922EPA	MAX931CPA
MAX912CSE+	MAX9144ESD+	MAX922EPA+	MAX931CSA
MAX912EPE	MAX9144EUD+	MAX922ESA	MAX931EPA
MAX912EPE+	MAX9201ESE+	MAX922ESA+	MAX931ESA
MAX912ESE	MAX9201EUE+	MAX922MJA	MAX932CPA
MAX912ESE+	MAX9202ESD+	MAX923CPA	MAX932CPA+
MAX912MJE	MAX9202EUD+	MAX923CPA+	MAX932CSA
MAX913CPA	MAX9203EKA+	MAX923CSA	MAX932CSA+
MAX913CPA+	MAX9203ESA+	MAX923CSA+	MAX932CUA+
MAX913CSA	MAX921CPA	MAX923CUA	MAX932EPA
MAX913CSA+	MAX921CPA+	MAX923CUA+	MAX932EPA+
MAX913EPA	MAX921CSA	MAX923EPA	MAX932ESA

# Multisim 14.0 Education Components

---

MAX932ESA+	MAX941ESA	MAX951EPA+	MAX954ESA+
MAX933CPA	MAX941ESA+	MAX951ESA+	MAX954EUA+
MAX933CPA+	MAX941EUA+	MAX951EUA+	MAX954MJA
MAX933CSA	MAX941MJA	MAX951MJA	MAX9550EUA+
MAX933CSA+	MAX942AUA+	MAX952CPA	MAX9550EZK+
MAX933CUA+	MAX942CPA	MAX952CSA	MAX9551EUA+
MAX933EPA	MAX942CPA+	MAX952EPA	MAX9552EUD+
MAX933EPA+	MAX942CSA	MAX952EPA+	MAX9600EUP+
MAX933ESA	MAX942CSA+	MAX952ESA	MAX9601EUP+
MAX933ESA+	MAX942CUA+	MAX952ESA+	MAX9602EUG+
MAX934CPE	MAX942EPA	MAX952EUA+	MAX9617AXT+
MAX934CPE+	MAX942EPA+	MAX952MJA	MAX9618AXA+
MAX934CSE	MAX942ESA	MAX953CPA	MAX9619AXT+
MAX934CSE+	MAX942ESA+	MAX953CSA	MAX961ESA
MAX934EPE	MAX942EUA+	MAX953EPA	MAX961ESA+
MAX934EPE+	MAX942MJA	MAX953EPA+	MAX961EUA+
MAX934ESE	MAX944CPD	MAX953ESA	MAX9620AXK+
MAX934ESE+	MAX944CPD+	MAX953ESA+	MAX9621AUB/V+
MAX941CPA	MAX944CSD	MAX953EUA+	MAX9621AUB/V+T
MAX941CPA+	MAX944CSD+	MAX953MJA	MAX9621AUB+
MAX941CSA	MAX944EPD	MAX954CPA	MAX9621AUB+T
MAX941CSA+	MAX944EPD+	MAX954CSA	MAX962ESA
MAX941CUA	MAX944ESD	MAX954EPA	MAX9636AXT+
MAX941EPA	MAX944ESD+	MAX954EPA+	MAX9637AXA+
MAX941EPA+	MAX944MJD	MAX954ESA	MAX9638AVB+



# Multisim 14.0 Education Components

---

MAX963ESA	MAX976ESA+	MAX990EUA+	MAX9928FABT+
MAX963ESD+	MAX976EUA+	MAX9910EXK+	MAX9928FAUA+
MAX9643TATA+T	MAX976MUA/PR2	MAX9911EWT+	MAX9929FABT+
MAX9643UATA+T	MAX977EEE+	MAX9911EXT+	MAX9929FAUA+
MAX9647AUK+T	MAX977ESD+	MAX9912EKA+	MAX992EKA+
MAX9647AXK+T	MAX978EEE+	MAX9913EUB+	MAX992ESA+
MAX964ESA	MAX978ESE+	MAX9915EXT+	MAX992EUA+
MAX9650ATA+	MAX985EBT+T	MAX9916EKA+	MAX9934FART+
MAX9650AUA+	MAX985ESA+	MAX9917EUB+	MAX9934FAUA+
MAX9650AZK+	MAX985EUK+	MAX9918ASA+	MAX9934TART+
MAX9651ATA+	MAX985EXK+	MAX9919FASA+	MAX9934TAUA+
MAX9651AUA+	MAX986ESA+	MAX9919NASA+	MAX993ESD+
MAX965ESA+	MAX986EUK+	MAX991EKA+	MAX993EUD+
MAX965EUA+	MAX986EXK+	MAX991ESA+	MAX9940AXK+
MAX9691EPA+	MAX987ESA+	MAX991EUA+	MAX9943ATT+T
MAX9691ESA+	MAX987EUK+	MAX9920ASA+	MAX9943AUA+
MAX9691EUA+	MAX987EXK+	MAX9924UAUB/V+	MAX9944ASA+
MAX9692EPE+	MAX988ESA+	MAX9924UAUB/V+ T	MAX9944ATA+T
MAX9692ESE+	MAX988EUK+	MAX9924UAUB+	MAX994ESD+
MAX9692EUB+	MAX988EXK+	MAX9924UAUB+T	MAX994EUD+
MAX9693EEE+	MAX989EKA+	MAX9926UAEE/V+	MAX995ESD+
MAX9693EPE+	MAX989ESA+	MAX9926UAEE/V+T	MAX995EUD+
MAX9693ESE+	MAX989EUA+	MAX9926UAEE+	MAX996ESD+
MAX975ESA+	MAX990EKA+	MAX9926UAEE+T	MAX996EUD+
MAX975EUA+	MAX990ESA+		MAX997ESA+

# Multisim 14.0 Education Components

---

MAX997EUA+	MBR0540T3G	MBR120ESFT3G	MBR160G
MAX998ESA+	MBR10100	MBR120LSFT1G	MBR160RLG
MAX998EUT+	MBR10100G	MBR120LSFT3G	MBR16100CTG
MAX999AAUK+5	MBR10100MFST1G	MBR120VLSFT1G	MBR1635
MAX999EUK+	MBR10100MFST3G	MBR120VLSFT3G	MBR1635G
MAXIM-MAXQ-HDR	MBR1035	MBR1240MFST1G	MBR1645
MB6S-E3/80	MBR1035G	MBR1240MFST3G	MBR1645G
MBD1057-C18	MBR1045	MBR130LSFT1G	MBR16H45-E3/45
MBD2057-C18	MBR1045G	MBR130T1	MBR1H100SFT3G
MBD3057-C18	MBR1045MFST1G	MBR130T1G	MBR20035CT
MBD4057-C18	MBR1045MFST3G	MBR130T3G	MBR20045CT
MBD5057-C18	MBR1060	MBR140ESFT1G	MBR20100
MBD770DWT1G	MBR1060G	MBR140ESFT3G	MBR20100CTG
MBR030	MBR1080G	MBR140SFT1G	MBR20100CTH
MBR040	MBR1090G	MBR140SFT3G	MBR20200CTG
MBR0520L	MBR10H100CTG	MBR150G	MBR2030CTLG
MBR0520LT1	MBR10H100CTHE3/ 45	MBR150RLG	MBR2035CT
MBR0520LT1G	MBR10H100-E3/45	MBR1520	MBR2045CT
MBR0520LT3G	MBR10L60CTG	MBR1530	MBR2045CTG
MBR0530	MBR1100G	MBR1535CT	MBR2045EMFST1G
MBR0530T1	MBR1100RLG	MBR1535CTG	MBR2045EMFST3G
MBR0530T1G	MBR12035CT	MBR1540	MBR2045MFST1G
MBR0530T3G	MBR12045CT	MBR1545CT	MBR2045MFST3G
MBR0540T1	MBR120ESFT1G	MBR1545CT-E3/45	MBR2060CTG
MBR0540T1G		MBR1545CTG	MBR2080CTG

# Multisim 14.0 Education Components

---

MBR2090CTG	MBR3045PT	MBR3520	MBR460MFST3G
MBR20H100CT/45	MBR3045PTG	MBR3535	MBR5100MFST1G
MBR20H100CTG	MBR3045STG	MBR3545	MBR5100MFST3G
MBR20H150CTG	MBR3045WTG	MBR3545H	MBR540MFST1G
MBR20H200CT-E3/45	MBR30H100CTG	MBR360G	MBR540MFST3G
MBR20L45CTG	MBR30H100MFST1G	MBR360RLG	MBR560MFST1G
MBR20L60CTG	MBR30H100MFST3G	MBR4015CTLG	MBR560MFST3G
MBR230LSFT1G	MBR30H150CTG	MBR4015LWT	MBR5825
MBR2520	MBR30H30CTG	MBR4015LWTG	MBR5825H
MBR2530	MBR30H60CTG	MBR4020	MBR5831
MBR2535CT	MBR30L45CTG	MBR40250G	MBR5831H
MBR2535CTG	MBR30L60CTG	MBR40250TG	MBR5H100MFST1G
MBR2535CTL	MBR3100G	MBR4030	MBR6035
MBR2535CTLG	MBR3100RLG	MBR4040	MBR6035B
MBR2540	MBR320M	MBR4045PT-E3/45	MBR6035PF
MBR2545CT	MBR320P	MBR4045PTG	MBR6045
MBR2545CTG	MBR330M	MBR4045WTG	MBR6045B
MBR2H100SFT3G	MBR330P	MBR4060PT-E3/45	MBR6045H
MBR30035CT	MBR340	MBR40H100WTG	MBR6045PF
MBR30045CT	MBR340G	MBR40L45CTG	MBR6045PTG
MBR3020CT	MBR340M	MBR40L60CTG	MBR6045WTG
MBR3035CT	MBR340P	MBR41H100CTG	MBR60H100CTG
MBR3035PT	MBR340RLG	MBR440MFST1G	MBR60L45CTG
MBR3045CT	MBR350RLG	MBR440MFST3G	MBR60L45WTG
		MBR460MFST1G	MBR6535

# Multisim 14.0 Education Components

---

MBR6545	MBRA1H100T3G	MBRB20H100CTT4 G	MBRD1035CTL G
MBR7030WTL	MBRA210ET3G		MBRD1035CTLG
MBR735	MBRA210LT3G	MBRB2515LG	MBRD1035CTLT4G
MBR735G	MBRA2H100T3G	MBRB2515LT4G	MBRD1045T4G
MBR745	MBRA320T3G	MBRB2535CTLG	MBRD320G
MBR745-E3/45	MBRA340T3G	MBRB2535CTLT4G	MBRD320RLG
MBR745G	MBRAF1100T3G	MBRB2545CTG	MBRD320T4G
MBR7520	MBRAF1540T3G	MBRB2545CTT4G	MBRD330G
MBR7530	MBRAF2H100T3G	MBRB3030CT	MBRD330RLG
MBR7535	MBRAF3200T3G	MBRB3030CTG	MBRD330T4G
MBR7540	MBRAF440T3G	MBRB3030CTL	MBRD340G
MBR7545	MBRB1045G	MBRB3030CTLG	MBRD340RLG
MBR760-E3/45	MBRB1045T4G	MBRB3030CTT4G	MBRD340T4G
MBR7H45-E3/45	MBRB1545CTG	MBRB3045CT-1G	MBRD350G
MBR8035	MBRB1545CTT4	MBRB30H30CT-1G	MBRD350RLG
MBR8045	MBRB1545CTT4G	MBRB30H60CT-1G	MBRD350T4G
MBR8H100MFST1G	MBRB1645T4G	MBRB30H60CTT4G	MBRD360G
MBR8H100MFST3G	MBRB20100CTG	MBRB4030	MBRD360RLG
MBRA120ET3G	MBRB20100CTT4	MBRB4030G	MBRD360T4
MBRA130LT3	MBRB20100CTT4G	MBRB4030T4G	MBRD360T4G
MBRA130LT3G	MBRB20200CTG	MBRB41H100CT-1G	MBRD5H100T4G
MBRA140T3	MBRB20200CTT4	MBRB41H100CTT4 G	MBRD620CTT4G
MBRA140T3G	MBRB20200CTT4G	MBRB60H100CTT4 G	MBRD630CTT4G
MBRA160T3	MBRB2060CTG		MBRD640CTT4
MBRA160T3G	MBRB2060CTT4G	MBRB8H100T4G	MBRD640CTT4G

# Multisim 14.0 Education Components

---

MBRD650CTG	MBRF40250TG	MBRS120T3G	MBRS360BT3G
MBRD650CTT4G	MBRL030	MBRS130LT3	MBRS360T3
MBRD660CTG	MBRL040	MBRS130LT3G	MBRS360T3G
MBRD660CTRLG	MBRM110ET1G	MBRS130T3G	MBRS410ET3G
MBRD660CTT4G	MBRM110ET3G	MBRS140T3	MBRS410LT3
MBRD835L	MBRM110LT1G	MBRS140T3G	MBRS410LT3G
MBRD835LG	MBRM110LT3G	MBRS1540T3G	MBRS420T3G
MBRD835LT4G	MBRM120ET1G	MBRS190T3	MBRS540T3
MBRF10H150CTG	MBRM120ET3G	MBRS190T3G	MBRS540T3G
MBRF10L60CTG	MBRM120LT1	MBRS2040LT3	MBT2222ADW1T1G
MBRF20100CTG	MBRM120LT1G	MBRS2040LT3G	MBT35200MT1
MBRF20200CTG	MBRM120LT3	MBRS230LT3G	MBT35200MT1G
MBRF2045CTG	MBRM120LT3G	MBRS240LT3	MBT3904DW1T1G
MBRF2060CTG	MBRM130LT1G	MBRS240LT3G	MBT3946DW1T1G
MBRF20H100CTG	MBRM130LT3	MBRS260T3G	MBT3946DW1T2G
MBRF20H150CTG	MBRM130LT3G	MBRS2H100T3G	MC1436CD
MBRF20L45CTG	MBRM140T1	MBRS3100T3G	MC1436CG
MBRF20L60CTG	MBRM140T1G	MBRS3200T3	MC1436CP1
MBRF20L80CTG	MBRM140T3	MBRS3200T3G	MC1436CU
MBRF2545CTG	MBRM140T3G	MBRS3201T3G	MC1436D
MBRF30H100CTG	MBRM1H100T3G	MBRS320T3	MC1436G
MBRF30H150CTG	MBRM2H100T3G	MBRS320T3G	MC1436P1
MBRF30H60CTG	MBRS1100T3	MBRS330T3G	MC1436U
MBRF30L45CTG	MBRS1100T3G	MBRS340T3	MC1437L
MBRF30L60CTG	MBRS120T3	MBRS340T3G	MC1437P

# Multisim 14.0 Education Components

---

MC1439G	MC1558FK	MC1747G	MC33071D
MC1439P1	MC1558G	MC1747L	MC33071DG
MC1456CG	MC1558JG	MC1748CG	MC33071DR2G
MC1456CP1	MC1558SG	MC1748CP1	MC33071P
MC1456G	MC1558SU	MC1748CU	MC33071PG
MC1456P1	MC1558U	MC1748G	MC33071U
MC1458CD	MC1709AG	MC1748U	MC33072ADG
MC1458CG	MC1709AU	MC1776CD	MC33072ADR2G
MC1458CP1	MC1709CG	MC1776CG	MC33072AP
MC1458CU	MC1709CP1	MC1776CP1	MC33072APG
MC1458D	MC1709CU	MC1776CU	MC33072D
MC1458G	MC1709G	MC1776G	MC33072DG
MC1458P	MC1741CD	MC1776U	MC33072DR2G
MC1458P1	MC1741CG	MC3301P	MC33072P
MC1458SD	MC1741CP1	MC3302DG	MC33072PG
MC1458SG	MC1741CU	MC3302DR2G	MC33072U
MC1458SP1	MC1741G	MC3302DTBR2G	MC33074ADG
MC1458SU	MC1741SCD	MC3302PG	MC33074ADR2G
MC1458U	MC1741SCG	MC3303D	MC33074ADTBG
MC1536G	MC1741SCP1	MC3303L	MC33074ADTBR2G
MC1536U	MC1741U	MC3303P	MC33074APG
MC1537L	MC1747CD	MC33071ADG	MC33074D
MC1539G	MC1747CG	MC33071ADR2G	MC33074DG
MC1556G	MC1747CL	MC33071AP	MC33074DR2G
MC1556U	MC1747CP2	MC33071APG	MC33074DTBG

# Multisim 14.0 Education Components

---

MC33074DTBR2G	MC33171DR2G	MC33272ADG	MC3403DG
MC33074L	MC33171P	MC33272APG	MC3403DR2G
MC33074P	MC33171PG	MC33272D	MC3403L
MC33074PG	MC33172D	MC33272P	MC3403N
MC33077D	MC33172P	MC33274ADG	MC3403P
MC33077DG	MC33174D	MC33274ADTBR2G	MC3403PG
MC33077DR2G	MC33174P	MC33274APG	MC3405L
MC33077P	MC33178D	MC33274D	MC3405P
MC33077PG	MC33178DG	MC33274P	MC34063ADG
MC33078D	MC33178DMR2G	MC33282D	MC34063ADR2G
MC33078DG	MC33178DR2G	MC33282P	MC34063AP1G
MC33078DR2G	MC33178P	MC33284D	MC34071D
MC33078P	MC33178PG	MC33284P	MC34071P
MC33078PG	MC33179D	MC33364D1G	MC34071U
MC33079D	MC33179DG	MC33364D1R2G	MC34080D
MC33079DG	MC33179DR2G	MC33364D2G	MC34080P
MC33079DR2G	MC33179DTBR2G	MC33364D2R2G	MC34084DW
MC33079P	MC33179P	MC3358P1	MC34084P
MC33079PG	MC33179PG	MC34001D	MC34161DG
MC33161DG	MC33181D	MC34001G	MC34161DMR2G
MC33161DMR2G	MC33181P	MC34001P	MC34161DR2G
MC33161DR2G	MC33182D	MC34001U	MC34161PG
MC33161PG	MC33182P	MC3401D	MC34181D
MC33171D	MC33184D	MC3401P	MC34181P
MC33171DG	MC33184P	MC3403D	MC3458D

# Multisim 14.0 Education Components

---

MC3458G	MC4741CD	MCP6001T-E/OT	MCP6021-I/ST
MC3458P1	MC4741CL	MCP6001T-I/LT	MCP6021T-E/OT
MC3458U	MC4741CP	MCP6001T-I/OT	MCP6022-I/P
MC3476G	MC4741L	MCP6001UT-E/OT	MCP6022-I/SN
MC3476P1	MCH3209-TL-E	MCP6001UT-I/OT	MCP6022-I/ST
MC3476U	MCH3377-TL-E	MCP6002-E/MC	MCP6023-I/P
MC35001G	MCH3377-TL-H	MCP6002-E/P	MCP6023-I/SN
MC35001U	MCH3383-TL-H	MCP6002-I/MS	MCP6023-I/ST
MC3503L	MCH3474-TL-E	MCP6002-I/P	MCP6024-I/P
MC3505L	MCH3474-TL-H	MCP6002-I/SN	MCP6024-I/SL
MC35071AU	MCH3484-TL-H	MCP6002T-E/MS	MCP6024-I/ST
MC35071U	MCH6203-TL-E	MCP6002T-E/SN	MCP602T-I/P
MC35080AU	MCH6320-TL-E	MCP6004-E/P	MCP602T-I/SN
MC35080U	MCH6321-TL-E	MCP6004-I/P	MCP602T-I/ST
MC35171U	MCH6336-TL-E	MCP6004-I/SL	MCP6031-E/MS
MC35181U	MCH6336-TL-H	MCP6004-I/ST	MCP6031-E/SN
MC3558G	MCH6337-TL-E	MCP6004T-E/SL	MCP6031T-E/OT
MC3558U	MCH6337-TL-H	MCP6004T-E/ST	MCP6032-E/MS
MC4558ACP1	MCH6421-TL-E	MCP601-I/P	MCP6032-E/SN
MC4558CD	MCH6436-TL-E	MCP601-I/SN	MCP6033-E/MS
MC4558CG	MCH6534-TL-E	MCP601-I/ST	MCP6033-E/SN
MC4558CP1	MCH6604-TL-E	MCP601T-I/OT	MCP6034-E/SL
MC4558CU	MCP6001RT-E/OT	MCP6021-E/MS	MCP6034-E/ST
MC4558G	MCP6001RT-I/OT	MCP6021-I/P	MCP603T-I/CH
MC4558U	MCP6001T-E/LT	MCP6021-I/SN	MCP603T-I/P



# Multisim 14.0 Education Components

---

MCP603T-I/SN	MCP6054T-E/ST	MCP609-I/P	MCP618-I/SN
MCP603T-I/ST	MCP6061T-E/MNY	MCP609-I/SL	MCP619-I/P
MCP6041-I/MS	MCP6061T-E/OT	MCP609-I/ST	MCP619-I/SL
MCP6041-I/P	MCP6061T-E/SN	MCP6141-I/MS	MCP619-I/ST
MCP6041-I/SN	MCP6062T-E/MNY	MCP6141-I/P	MCP621ST-E/OT
MCP6041T-I/OT	MCP6062T-E/SN	MCP6141-I/SN	MCP621T-E/MNY
MCP6042-I/MS	MCP6064T-E/SL	MCP6141T-E/OT	MCP621T-E/SN
MCP6042-I/P	MCP6064T-E/ST	MCP6142-I/MS	MCP622T-E/MF
MCP6042-I/SN	MCP606-I/P	MCP6142-I/P	MCP622T-E/SN
MCP6043-I/MS	MCP606-I/SN	MCP6142-I/SN	MCP6231-E/MC
MCP6043-I/P	MCP606-I/ST	MCP6143-I/MS	MCP6231-E/MS
MCP6043-I/SN	MCP606T-I/OT	MCP6143-I/P	MCP6231-E/P
MCP6043T-I/CH	MCP6071T-E/MNY	MCP6143-I/SN	MCP6231-E/SN
MCP6044-I/P	MCP6071T-E/OT	MCP6143T-E/CH	MCP6231RT-E/OT
MCP6044-I/SL	MCP6071T-E/SN	MCP6144-I/P	MCP6231T-E/OT
MCP6044-I/ST	MCP6072T-E/MNY	MCP6144-I/SL	MCP6231UT-E/LT
MCP604T-I/P	MCP6072T-E/SN	MCP6144-I/ST	MCP6231UT-E/OT
MCP604T-I/SL	MCP6074T-E/SL	MCP616-I/MS	MCP6232-E/MS
MCP604T-I/ST	MCP6074T-E/ST	MCP616-I/P	MCP6232-E/P
MCP6051T-E/MNY	MCP607-I/P	MCP616-I/SN	MCP6232-E/SN
MCP6051T-E/OT	MCP607-I/SN	MCP617-I/MS	MCP6232T-E/MNY
MCP6051T-E/SN	MCP607-I/ST	MCP617-I/P	MCP6234-E/P
MCP6052T-E/MNY	MCP608-I/P	MCP617-I/SN	MCP6234-E/SL
MCP6052T-E/SN	MCP608-I/SN	MCP618-I/MS	MCP6234-E/ST
MCP6054T-E/SL	MCP608-I/ST	MCP618-I/P	MCP623T-E/CHY

# Multisim 14.0 Education Components

---

MCP6241-E/MC	MCP6272-E/SN	MCP6284-E/SL	MCP631T-E/MNY
MCP6241-E/MS	MCP6273-E/MS	MCP6284-E/ST	MCP631T-E/OT
MCP6241-E/P	MCP6273-E/P	MCP6285-E/MS	MCP631T-E/SN
MCP6241-E/SN	MCP6273-E/SN	MCP6285-E/P	MCP632T-E/MF
MCP6241RT-E/OT	MCP6273T-E/CH	MCP6285-E/SN	MCP632T-E/SN
MCP6241T-E/OT	MCP6273T-E/SN	MCP6286T-E/OT	MCP633T-E/CHY
MCP6241UT-E/LT	MCP6274-E/P	MCP6291-E/MS	MCP633T-E/SN
MCP6241UT-E/OT	MCP6274-E/SL	MCP6291-E/P	MCP635T-E/MF
MCP6242-E/MS	MCP6274-E/ST	MCP6291-E/SN	MCP635T-E/UN
MCP6242-E/P	MCP6275-E/MS	MCP6291RT-E/OT	MCP6401RT-E/OT
MCP6242-E/SN	MCP6275-E/P	MCP6291T-E/OT	MCP6401T-E/LT
MCP6244-E/P	MCP6275-E/SN	MCP6292-E/MS	MCP6401T-E/OT
MCP6244-E/SL	MCP6281-E/MS	MCP6292-E/P	MCP6401T-H/OT
MCP6244-E/ST	MCP6281-E/P	MCP6292-E/SN	MCP6401UT-E/OT
MCP624T-E/SL	MCP6281-E/SN	MCP6293-E/MS	MCP6402T-E/MNY
MCP624T-E/ST	MCP6281RT-E/OT	MCP6293-E/P	MCP6402T-E/SN
MCP625T-E/MF	MCP6281T-E/OT	MCP6293-E/SN	MCP6402T-H/SN
MCP625T-E/UN	MCP6282-E/MS	MCP6293T-E/CH	MCP6404T-E/SL
MCP6271-E/MS	MCP6282-E/P	MCP6294-E/P	MCP6404T-E/ST
MCP6271-E/P	MCP6282-E/SN	MCP6294-E/SL	MCP6404T-H/SL
MCP6271-E/SN	MCP6283-E/MS	MCP6294-E/ST	MCP6406T-H/OT
MCP6271RT-E/OT	MCP6283-E/P	MCP6295-E/MS	MCP6407T-H/SN
MCP6271T-E/OT	MCP6283-E/SN	MCP6295-E/P	MCP6409T-H/SL
MCP6272-E/MS	MCP6283T-E/CH	MCP6295-E/SN	MCP6421T-E/LTY
MCP6272-E/P	MCP6284-E/P	MCP629T-E/ML	MCP6421T-E/OT

# Multisim 14.0 Education Components

---

MCP6441T-E/LT	MCP6484-E/SL	MCP6541RT-E/OT	MCP6544T-I/ST
MCP6441T-E/OT	MCP6484-E/ST	MCP6541T-E/MS	MCP6546-E/P
MCP6442T-E/MNY	MCP6484T-E/SL	MCP6541T-E/OT	MCP6546-I/MS
MCP6442T-E/MS	MCP6484T-E/ST	MCP6541T-E/SN	MCP6546-I/P
MCP6442T-E/SN	MCP6491T-E/LTY	MCP6541T-I/LT	MCP6546-I/SN
MCP6444T-E/SL	MCP6491T-E/OT	MCP6541T-I/OT	MCP6546RT-E/OT
MCP6444T-E/ST	MCP6492-E/MS	MCP6541UT-E/OT	MCP6546RT-I/OT
MCP6471T-E/LTY	MCP6492-E/SN	MCP6541UT-I/LT	MCP6546T-E/MS
MCP6471T-E/OT	MCP6492T-E/MNY	MCP6542-E/P	MCP6546T-E/OT
MCP6472-E/MS	MCP6492T-E/MS	MCP6542-I/MS	MCP6546T-E/SN
MCP6472-E/SN	MCP6492T-E/SN	MCP6542-I/P	MCP6546T-I/LT
MCP6472T-E/MNY	MCP6494-E/SL	MCP6542-I/SN	MCP6546T-I/MS
MCP6472T-E/MS	MCP6494-E/ST	MCP6542T-E/MS	MCP6546T-I/OT
MCP6472T-E/SN	MCP6494T-E/SL	MCP6542T-E/SN	MCP6546T-I/SN
MCP6474-E/SL	MCP6494T-E/ST	MCP6543-E/P	MCP6546UT-E/OT
MCP6474-E/ST	MCP651ST-E/OT	MCP6543-I/P	MCP6546UT-I/LT
MCP6474T-E/SL	MCP651T-E/MNY	MCP6543-I/SN	MCP6547-E/P
MCP6474T-E/ST	MCP651T-E/SN	MCP6543T-E/MS	MCP6547-I/MS
MCP6481T-E/LTY	MCP652T-E/MF	MCP6543T-E/SN	MCP6547-I/P
MCP6481T-E/OT	MCP652T-E/SN	MCP6543T-I/MS	MCP6547-I/SN
MCP6482-E/MS	MCP653T-E/CHY	MCP6544-E/P	MCP6547T-E/MS
MCP6482-E/SN	MCP6541-E/P	MCP6544T-E/SL	MCP6547T-E/SN
MCP6482T-E/MNY	MCP6541-I/MS	MCP6544T-E/ST	MCP6547T-I/MS
MCP6482T-E/MS	MCP6541-I/P	MCP6544T-I/P	MCP6547T-I/SN
MCP6482T-E/SN	MCP6541-I/SN	MCP6544T-I/SL	MCP6548-E/P

# Multisim 14.0 Education Components

---

MCP6548-I/MS	MCP6564T-E/SL	MCP662T-E/SN	MCP6H81T-E/MNY
MCP6548-I/P	MCP6564T-E/ST	MCP663T-E/CHY	MCP6H81T-E/SN
MCP6548-I/SN	MCP6566RT-E/OT	MCP663T-E/SN	MCP6H82-E/SN
MCP6548T-E/MS	MCP6566T-E/LT	MCP664T-E/SL	MCP6H82T-E/MNY
MCP6548T-E/SN	MCP6566T-E/OT	MCP664T-E/ST	MCP6H82T-E/SN
MCP6548T-I/MS	MCP6566UT-E/OT	MCP665T-E/MF	MCP6H84-E/SL
MCP6548T-I/SN	MCP6567T-E/MS	MCP665T-E/UN	MCP6H84-E/ST
MCP6549-E/P	MCP6567T-E/SN	MCP669T-E/ML	MCP6H84T-E/SL
MCP6549-I/P	MCP6569T-E/SL	MCP6H01T-E/MNY	MCP6H84T-E/ST
MCP6549-I/SL	MCP6569T-E/ST	MCP6H01T-E/SN	MCP6H91T-E/MNY
MCP6549-I/ST	MCP659T-E/ML	MCP6H02T-E/MNY	MCP6H91T-E/SN
MCP6549T-E/SL	MCP65R41T- 1202E/CHY	MCP6H02T-E/SN	MCP6H92T-E/MNY
MCP6549T-E/ST		MCP6H04T-E/SL	MCP6H92T-E/SN
MCP6549T-I/SL	MCP65R41T- 2402E/CHY	MCP6H04T-E/ST	MCP6H94T-E/SL
MCP6549T-I/ST	MCP65R46T- 1202E/CHY	MCP6H71-E/SN	MCP6H94T-E/ST
MCP654T-E/SL		MCP6H71T-E/MNY	MCP6L01RT-E/OT
MCP654T-E/ST	MCP65R46T- 2402E/CHY	MCP6H71T-E/SN	MCP6L01T-E/LT
MCP655T-E/MF	MCP660T-E/ML	MCP6H72-E/SN	MCP6L01T-E/OT
MCP655T-E/UN	MCP660T-E/SL	MCP6H72T-E/MNY	MCP6L01UT-E/OT
MCP6561RT-E/OT	MCP660T-E/ST	MCP6H72T-E/SN	MCP6L02T-E/MS
MCP6561T-E/LT	MCP661T-E/OT	MCP6H74-E/SL	MCP6L02T-E/SN
MCP6561T-E/OT	MCP661T-E/SN	MCP6H74-E/ST	MCP6L04T-E/SL
MCP6561UT-E/OT	MCP662T-E/MF	MCP6H74T-E/SL	MCP6L04T-E/ST
MCP6562T-E/MS	MCP662T-E/MS	MCP6H74T-E/ST	MCP6L1RT-E/OT
MCP6562T-E/SN		MCP6H81-E/SN	MCP6L1T-E/MS

# Multisim 14.0 Education Components

---

MCP6L1T-E/OT	MCP6V01T-E/MNY	MCP6V31UT-E/LT	MCR3818_4
MCP6L1T-E/SN	MCP6V01T-E/SN	MCP6V31UT-E/OT	MCR3818_6
MCP6L2T-E/MS	MCP6V02-E/MD	MCR08BT1G	MCR3818_8
MCP6L2T-E/SN	MCP6V02-E/SN	MCR08MT1G	MCR3835_1
MCP6L4T-E/SL	MCP6V03-E/MNY	MCR100-3G	MCR3835_10
MCP6L4T-E/ST	MCP6V03-E/SN	MCR100-3RLG	MCR3835_2
MCP6L71RT-E/OT	MCP6V06-E/SN	MCR1906_2	MCR3835_3
MCP6L71T-E/MS	MCP6V06T-E/MNY	MCR1906_3	MCR3835_4
MCP6L71T-E/OT	MCP6V07-E/MD	MCR1906_4	MCR3835_5
MCP6L71T-E/SN	MCP6V07-E/SN	MCR1906_6	MCR3835_6
MCP6L72T-E/MS	MCP6V08-E/SN	MCR1906_8	MCR3835_7
MCP6L72T-E/SN	MCP6V08T-E/MNY	MCR22_2	MCR3835_8
MCP6L74T-E/SL	MCP6V11T-E/OT	MCR22_3	MCR3835_9
MCP6L74T-E/ST	MCP6V11UT-E/LT	MCR22_4	MCR3935_1
MCP6L91RT-E/OT	MCP6V11UT-E/OT	MCR22_6	MCR3935_10
MCP6L91T-E/MS	MCP6V26T-E/MNY	MCR22_8	MCR3935_2
MCP6L91T-E/OT	MCP6V26T-E/MS	MCR220_5	MCR3935_3
MCP6L91T-E/SN	MCP6V26T-E/SN	MCR220_7	MCR3935_4
MCP6L92T-E/MS	MCP6V27T-E/MD	MCR220_9	MCR3935_5
MCP6L92T-E/SN	MCP6V27T-E/MS	MCR221_5	MCR3935_6
MCP6L94T-E/SL	MCP6V27T-E/SN	MCR221_7	MCR3935_7
MCP6L94T-E/ST	MCP6V28T-E/MNY	MCR221_9	MCR3935_8
MCP6N11-001E/SN	MCP6V28T-E/MS	MCR3818_10	MCR3935_9
MCP6N11T-001E/MNY	MCP6V28T-E/SN	MCR3818_2	MCR703AT4G
	MCP6V31T-E/OT	MCR3818_3	MCR706AT4G

# Multisim 14.0 Education Components

---

MCR716T4G	MDA920A9	MHD20N06C	MJ15022G
MCR8SNG	MDA970A1	MHD20N06G	MJ15023G
MCT6	MDA970A2	MHD20N06P	MJ15024G
MDA2500	MDA970A3	MICRO_4BIT_ALU	MJ15025G
MDA2501	MDA970A5	MINI-DIN3	MJ21193G
MDA2502	MDA970A6	MINI-DIN3S	MJ21194G
MDA2504	MDA980-1	MINI-DIN4	MJ21195G
MDA2506	MDA980-2	MINI-DIN4S	MJ21196G
MDA3500	MDA980-3	MINI-DIN5	MJ2955G
MDA3501	MDA980-4	MINI-DIN5S	MJ4502G
MDA3502	MDA980-5	MINI-DIN6	MJ802G
MDA3504	MDA980-6	MINI-DIN6S	MJB41CG
MDA3506	MDA990-1	MIPS-EJTAG-HDR	MJB41CT4G
MDA3508	MDA990-2	MJ11012G	MJB42CT4G
MDA3510	MDA990-3	MJ11015G	MJB44H11G
MDA3550	MDA990-4	MJ11016G	MJB44H11T4
MDA3551	MDA990-5	MJ11028G	MJB44H11T4G
MDA920A1	MDA990-6	MJ11032G	MJB45H11G
MDA920A2	MGP11N60ED	MJ11033G	MJB45H11T4
MDA920A3	MGSF1N02LT1G	MJ14002G	MJB45H11T4G
MDA920A4	MGSF1N03LT1G	MJ15001G	MJD112-1G
MDA920A5	MGSF1P02LT1	MJ15003G	MJD112G
MDA920A6	MGSF2N02ELT1G	MJ15004G	MJD112RLG
MDA920A7	MGSF3441VT1	MJ15015G	MJD112T4G
MDA920A8	MGW21N60ED	MJ15016G	MJD117-1G

# Multisim 14.0 Education Components

---

MJD117G	MJD3055G	MJD44H11-1G	MJE15033
MJD117RLG	MJD3055T4G	MJD44H11G	MJE15033G
MJD117T4G	MJD31C1G	MJD44H11RLG	MJE15034G
MJD122G	MJD31CG	MJD44H11T4G	MJE15035G
MJD122T4G	MJD31CRLG	MJD44H11T5G	MJE170G
MJD127G	MJD31CT4G	MJD45H11-1G	MJE171G
MJD127T4	MJD31T4G	MJD45H11G	MJE172G
MJD127T4G	MJD32CG	MJD45H11RLG	MJE18002G
MJD148T4	MJD32CRLG	MJD45H11T4G	MJE18004G
MJD148T4G	MJD32CT4	MJD47G	MJE18006G
MJD200	MJD32CT4G	MJD47T4G	MJE18008G
MJD200G	MJD32RLG	MJD50G	MJE180G
MJD200RLG	MJD32T4G	MJD50T4G	MJE181G
MJD200T4G	MJD340G	MJD5731T4G	MJE182G
MJD210G	MJD340RLG	MJD6039T4G	MJE200G
MJD210RLG	MJD340T4G	MJE13003G	MJE210G
MJD210T4	MJD350G	MJE13005G	MJE243G
MJD210T4G	MJD350T4G	MJE13007G	MJE253G
MJD243G	MJD41CRLG	MJE13009G	MJE270G
MJD243T4G	MJD41CT4G	MJE15028G	MJE271G
MJD253-1G	MJD42C1G	MJE15029G	MJE2955TG
MJD253T4G	MJD42CG	MJE15030G	MJE3055TG
MJD2955-1G	MJD42CRLG	MJE15031G	MJE340
MJD2955G	MJD42CT4G	MJE15032	MJE340G
MJD2955T4G	MJD44E3T4G	MJE15032G	MJE3439G

# Multisim 14.0 Education Components

---

MJE344G	MJF2955G	MKP3V240RLG	MM5Z12VT1G
MJE350	MJF3055G	MM3Z10VT1G	MM5Z15VT1G
MJE350G	MJF31CG	MM3Z12VST1G	MM5Z16VT1G
MJE371G	MJF32CG	MM3Z12VT1G	MM5Z18VT1G
MJE4343G	MJF44H11G	MM3Z15VST1G	MM5Z20VT1G
MJE4353G	MJF45H11G	MM3Z15VT1G	MM5Z24VT1G
MJE5730G	MJH11021G	MM3Z18VT1G	MM5Z27VT1G
MJE5731AG	MJH11022G	MM3Z20VT1G	MM5Z2V4ST1G
MJE5731G	MJH6284G	MM3Z2V4T1G	MM5Z2V4T1G
MJE5742G	MJH6287G	MM3Z2V7T1G	MM5Z2V7T1G
MJE5850G	MJL1302A	MM3Z30VT1G	MM5Z33VT1G
MJE5851G	MJL1302AG	MM3Z36VT1G	MM5Z36VT1G
MJE5852G	MJL21193G	MM3Z39VT1G	MM5Z3V0T1G
MJE700G	MJL21194G	MM3Z3V0T1G	MM5Z3V3T1G
MJE702G	MJL21195G	MM3Z3V3ST1G	MM5Z3V6T1G
MJE703G	MJL21196G	MM3Z3V6T1G	MM5Z47VT1G
MJE800G	MJL3281AG	MM3Z3V9T1G	MM5Z4V3T1G
MJE802G	MJL4281AG	MM3Z43VT1G	MM5Z4V7ST1G
MJE803G	MJL4302AG	MM3Z4V3ST1G	MM5Z4V7ST5G
MJF122G	MJW18020G	MM3Z4V7T1G	MM5Z4V7T1G
MJF127G	MJW21196G	MM3Z5V1T1G	MM5Z5V1ST1G
MJF15030G	MJW3281AG	MM3Z5V6ST1G	MM5Z5V1T1G
MJF15031G	MKP3V120G	MM3Z6V8ST1G	MM5Z5V6ST1G
MJF18004G	MKP3V120RLG	MM3Z8V2ST1G	MM5Z5V6T1G
MJF18008G	MKP3V240G	MM5Z10VT1G	MM5Z6V2ST1G



# Multisim 14.0 Education Components

---

MM5Z6V2T1G	MMBD7000LT1	MMBR931L	MMBT3906TT1G
MM5Z6V8ST1G	MMBD7000LT1G	MMBR931LT1	MMBT4401LT1
MM5Z6V8T1G	MMBD7000LT3G	MMBR941	MMBT4401LT1G
MM5Z7V5T1G	MMBD717LT1G	MMBR941LT1	MMBT4401LT3G
MM5Z8V2ST1G	MMBD914	MMBR951AL	MMBT4401M3T5G
MM5Z8V2T1G	MMBD914LT1	MMBR951L	MMBT4403LT1
MM5Z9V1ST1G	MMBD914LT1G	MMBR951LT1	MMBT4403LT1G
MM5Z9V1T1G	MMBD914LT3G	MMBT2222A	MMBT4403LT3G
MMBD101LT1G	MMBF0201NLT1	MMBT2222ALT1	MMBT4403M3T5G
MMBD1201	MMBF0201NLT1G	MMBT2222ALT1G	MMBT489LT1G
MMBD1202	MMBF170LT1G	MMBT2222ALT3G	MMBT5401LT1
MMBD1203	MMBF4393LT1G	MMBT2369ALT1G	MMBT5401LT1G
MMBD1204	MMBF4393LT3G	MMBT2484LT1G	MMBT5401LT3G
MMBD1205	MMBFJ175LT1G	MMBT2484LT3G	MMBT5551LT1
MMBD2835LT1G	MMBFJ177LT1G	MMBT2907ALT1	MMBT5551LT1G
MMBD2836LT1G	MMBFJ309LT1G	MMBT2907ALT1G	MMBT5551LT3G
MMBD2837LT1G	MMBR5031LT1	MMBT2907ALT3G	MMBT5551M3T5G
MMBD2838LT1G	MMBR521LT1	MMBT2907AM3T5 G	MMBT589LT1
MMBD301LT1	MMBR571L	MMBT3904	MMBT589LT1G
MMBD301LT1G	MMBR571LT1	MMBT3904LT1	MMBT6428LT1G
MMBD301LT3G	MMBR901_B	MMBT3904LT1G	MMBT6429LT1G
MMBD301M3T5G	MMBR901L	MMBT3904LT3G	MMBT6517LT1
MMBD352LT1G	MMBR901LT1	MMBT3904TT1G	MMBT6517LT1G
MMBD353LT1G	MMBR911LT1	MMBT3906	MMBT6517LT3G
MMBD4148	MMBR920LT1		MMBT6520LT1

# Multisim 14.0 Education Components

---

MMBT6520LT1G	MMBZ12VAL	MMBZ5232BLT1G	MMQA15VT1G
MMBTA06LT1	MMBZ12VDL	MMBZ5240BLT1G	MMQA20VT1G
MMBTA06LT1G	MMBZ15VAL	MMBZ5242BLT1G	MMQA20VT3G
MMBTA06LT3G	MMBZ15VALT1	MMBZ5242BLT3G	MMQA5V6T1G
MMBTA06WT1G	MMBZ15VALT1G	MMBZ5248BLT1G	MMQA5V6T3G
MMBTA14LT1G	MMBZ15VDL	MMBZ5248BLT3G	MMQA6V2T1G
MMBTA42	MMBZ15VDLT1G	MMBZ5254BLT1G	MMSD301T1
MMBTA42LT1	MMBZ15VDLT3G	MMBZ5256BLT1G	MMSD301T1G
MMBTA42LT1G	MMBZ18VAL	MMBZ5270BLT1G	MMSD4148T1
MMBTA42LT3G	MMBZ18VCL	MMBZ5V6AL	MMSD4148T1G
MMBTA56LT1	MMBZ20VAL	MMBZ5V6ALT1G	MMSD4148T3G
MMBTA56LT1G	MMBZ20VALT1G	MMBZ5V6ALT3G	MMSF3P02HD
MMBTA56LT3G	MMBZ20VCL	MMBZ6V2AL	MMSZ10T1G
MMBTA63LT1G	MMBZ27VAL	MMBZ6V8AL	MMSZ12T1G
MMBTA92	MMBZ27VALT1G	MMBZ9V1AL	MMSZ2V7T1G
MMBTA92LT1G	MMBZ27VALT3G	MMDF3N04HD	MMSZ2V7T3G
MMBTA92LT3G	MMBZ27VCL	MMDF6N03HD	MMSZ3V3T1G
MMBTH10-4LT1G	MMBZ27VCLT1G	MMDL770T1G	MMSZ4678T1G
MMBTH10LT1G	MMBZ33VAL	MMDL914T1	MMSZ4679T1G
MMBTH10LT3G	MMBZ33VALT1G	MMDL914T1G	MMSZ4681T1G
MMBV105GLT1G	MMBZ33VCL	MMDL914T3G	MMSZ4683T1G
MMBV3401LT1G	MMBZ5221BLT1G	MMFT5P03HD	MMSZ4688T1G
MMBV3401LT3	MMBZ5222BLT1G	MMFT960T1G	MMSZ4689T1G
MMBV3401LT3G	MMBZ5231BLT1G	MMG05N60D	MMSZ4689T3G
MMBZ10VAL	MMBZ5231BLT3G	MMJT350T1G	MMSZ4690T1G

# Multisim 14.0 Education Components

---

MMSZ4690T3G	MMSZ5245BT1G	MMUN2113LT3G	MOS_N
MMSZ4691T1G	MMSZ5246BT1G	MMUN2114LT1G	MOS_N_4T
MMSZ4692T1G	MMSZ5254BT1G	MMUN2114LT3G	MOS_N_4T_DEP
MMSZ4696T1G	MMSZ5258BT1G	MMUN2115LT1G	MOS_N_DEP
MMSZ4699T1G	MMSZ5258BT3G	MMUN2116LT1G	MOS_P
MMSZ4705T1G	MMSZ5259BT1G	MMUN2130LT1G	MOS_P_4T
MMSZ4706T1G	MMSZ5260BT1G	MMUN2131LT1G	MOS_P_4T_DEP
MMSZ4707T1G	MMSZ5262BT1G	MMUN2132LT1G	MOS_P_DEP
MMSZ4715T1G	MMSZ5263BT1G	MMUN2134LT1G	MOSFET_DIODE_THERMAL
MMSZ5221BT1G	MMT05B230T3G	MMUN2211LT1G	Mosfet1_3TEN
MMSZ5222BT1G	MMT05B260T3G	MMUN2211LT3G	MOTOR_1A
MMSZ5225BT1G	MMT05B310T3G	MMUN2212LT1G	MOTOR_1C
MMSZ5226BT1G	MMT05B350T3G	MMUN2213LT1G	MOTOR_2A
MMSZ5228BT1G	MMT08B064T3G	MMUN2214LT1G	MOTOR_2C
MMSZ5231BT1G	MMT08B260T3G	MMUN2215LT1G	MOTOR_3A
MMSZ5231BT3G	MMT08B310T3G	MMUN2216LT1G	MOTOR_3C
MMSZ5234BT1G	MMT08B350T3G	MMUN2231LT1G	MOTOR_4A
MMSZ5235BT1G	MMT10B230T3G	MMUN2232LT1G	MOTOR_4C
MMSZ5235BT3G	MMT10B260T3G	MMUN2233LT1G	Motor_dc1
MMSZ5236BT1G	MMT10B310T3G	MMUN2234LT1G	MOTOR_RATED
MMSZ5239BT1G	MMT10B350T3G	MMUN2238LT1G	MOTOR_VIRTUAL
MMSZ5240BT1G	MMUN2111LT1G	MMVL3401T1G	MPC100AP
MMSZ5242BT1G	MMUN2111LT3G	MOC8101_BASSO	MPC100AU
MMSZ5242BT3G	MMUN2112LT1G	MONOSTABLE_VIRTUAL	MPC102AP
MMSZ5243BT1G	MMUN2113LT1G		

# Multisim 14.0 Education Components

---

MPC102AU	MPS3704	MPS6571	MPSA56ZL1G
MPC104AP	MPS3707	MPS8098	MPSA70
MPC506AP	MPS3711	MPS8099	MPSA92
MPC506AU	MPS3826	MPS8598	MPSA93
MPC507AP	MPS3827	MPSA05	MPSH10
MPC507AU	MPS3904	MPSA06	MPSL01
MPC508AP	MPS5172	MPSA06G	MPSL51
MPC508AU	MPS5179	MPSA06RL1G	MPSW01
MPC509AP	MPS6512	MPSA06RLG	MPSW01A
MPC509AU	MPS6513	MPSA06RLRAG	MPSW06G
MPC-BDM-HDR	MPS6514	MPSA06RLRMG	MPSW06RLRAG
MPS2907AG	MPS6515	MPSA06RLRPG	MPSW10
MPS2907ARLG	MPS6516	MPSA10	MPSW42
MPS2907ARLRAG	MPS6517	MPSA18	MPSW45G
MPS2924	MPS6518	MPSA20	MPSW51
MPS2925	MPS6520	MPSA42	MPSW51A
MPS2926	MPS6521	MPSA42G	MPSW51AG
MPS3392	MPS6522	MPSA43	MPSW51ARLRAG
MPS3393	MPS6523	MPSA43G	MPSW51ARLRPG
MPS3395	MPS6531	MPSA55	MPSW51G
MPS3638A	MPS6533	MPSA56	MPSW55
MPS3644	MPS6534	MPSA56G	MPSW56
MPS3646	MPS6562	MPSA56RLRAG	MPX2010DP
MPS3702	MPS6565	MPSA56RLRMG	MPX2050DP
MPS3703	MPS6566	MPSA56RLRPG	MPX2100DP

# Multisim 14.0 Education Components

---

MPX2200DP	MR2506	MR754	MR860
MPZ2012S101A	MR2508	MR756	MR861
MPZ2012S221A	MR2510	MR810	MR862
MPZ2012S300A	MR327	MR811	MR864
MPZ2012S331A	MR328	MR812	MR866
MPZ3216S500A	MR330	MR813	MR870
MR1120	MR331	MR814	MR871
MR1366	MR500	MR816	MR872
MR1376	MR5005	MR817	MR874
MR1386	MR501	MR818	MR876
MR1396	MR5010	MR820	MRA4003T3G
MR2400	MR502	MR821	MRA4004T3G
MR2400F	MR5020	MR822	MRA4005T1G
MR2401	MR5030	MR824	MRA4005T3G
MR2401F	MR504	MR826	MRA4006T3G
MR2402	MR5040	MR830	MRA4007T3G
MR2402F	MR5059	MR831	MRF5211LT1
MR2404	MR506	MR832	MRF5711L
MR2404F	MR5060	MR834	MRF5711LT1
MR2406	MR5061	MR836	MRF5812
MR2406F	MR508	MR850	MRF8372
MR2500	MR510	MR851	MRF9011L
MR2501	MR750	MR852	MRF9011LT1
MR2502	MR751	MR854	MRF9011LT1_A
MR2504	MR752	MR856	MRF9011LT1_B

# Multisim 14.0 Education Components

---

MRF917T1	MSRD620CTT4RG	MTD4P06	MTP2N50
MRF927T1	MSRF1560G	MTD5N06	MTP2P50
MRF9331LT1	MSRF860G	MTD5P06V	MTP2P50EG
MRF9411BL	MSS1P3LHM3/89A	MTD6N15T4G	MTP3055E/MC
MRF9411L	MSS1P4HM3/89A	MTD6N20E	MTP3055V
MRF9411LT1	MSS1P6HM3/89A	MTD6N20ET4G	MTP3055VL
MRF947	MSS2P3HM3/89A	MTD6P10E	MTP30N08M
MRF947T1	MT4C4ME8DJ-5	MTDF1N03HD	MTP35N06E
MRF949T1	MTB20N20E	MTH13N50	MTP3N100
MRF9511AL	MTB23P06V	MTH30N20	MTP40N06M
MRF9511L	MTB2P50E	MTH5N100	MTP4N50
MRF9511LT1	MTB50P03HDL	MTH8N60	MTP4N85
MRS1504T3G	MTB50P03HDLT4G	MTM10N100E	MTP50N05EL
MSB92T1G	MTD10P06HDL	MTM15N40	MTP50N06E
MSD1328-RT1G	MTD15N06V	MTM24N50E	MTP6N60
MSD602-RT1G	MTD1N60E	MTM26N40E	MTP6N60/MC
MSE1PJHM3/89A	MTD1N80E	MTM8N60	MTP75N05C
MSP3V3HM3/89A	MTD20N06HD	MTP10N05E/MC	MTP7N20
MSQA6V1W5T2G	MTD20P03HDL	MTP12P10	MTP8N50E
MSR1560G	MTD2955E	MTP15N05E	MTP8P10
MSR860G	MTD2N50E	MTP15N06E	MTSF3N02HD
MSRD620CTG	MTD3055V	MTP20P06	MULTIPLIER
MSRD620CTRG	MTD3055VL	MTP25N06	MUN2111T1G
MSRD620CTT4	MTD3N25E	MTP25N06L	MUN2112T1G
MSRD620CTT4G	MTD4N20E	MTP25N10E	MUN2113T1G

# Multisim 14.0 Education Components

---

MUN2114T1G	MUN5112DW1T1G	MUN5214DW1T1G	MUN5334DW1T1G
MUN2115T1G	MUN5112T1G	MUN5214T1G	MUN5335DW1T1G
MUN2135T1G	MUN5113DW1T1G	MUN5215DW1T1G	MUN5336DW1T1G
MUN2138T1G	MUN5113T1G	MUN5215T1G	MUR10005CT
MUN2141T1G	MUN5113T3G	MUN5216DW1T1G	MUR10010CT
MUN2211T1	MUN5114DW1T1G	MUN5230DW1T1G	MUR10015CT
MUN2211T1G	MUN5114T1G	MUN5230T1G	MUR10020CT
MUN2211T3G	MUN5115DW1T1G	MUN5232DW1T1G	MUR10150E
MUN2212T1G	MUN5115T1G	MUN5232T1G	MUR105
MUN2213T1	MUN5116DW1T1G	MUN5233DW1T1G	MUR105G
MUN2213T1G	MUN5131T1G	MUN5233T1G	MUR105RLG
MUN2214T1G	MUN5132T1G	MUN5235DW1T1G	MUR110
MUN2214T3G	MUN5133DW1T1G	MUN5237DW1T1G	MUR1100EG
MUN2215T1G	MUN5133T1G	MUN5238T1G	MUR1100ERLG
MUN2216T1G	MUN5135DW1T1G	MUN5240T1G	MUR110G
MUN2230T1G	MUN5135T1G	MUN5241T1G	MUR110RLG
MUN2232T1G	MUN5140T1G	MUN5311DW1T1G	MUR115
MUN2233T1G	MUN5211DW1T1G	MUN5312DW1T1G	MUR115G
MUN2234T1G	MUN5211T1	MUN5312DW1T2G	MUR115RLG
MUN2236T1G	MUN5211T1G	MUN5313DW1T1G	MUR120G
MUN2237T1G	MUN5212DW1T1G	MUN5314DW1T1G	MUR120RLG
MUN2238T1G	MUN5212T1G	MUN5315DW1T1G	MUR130G
MUN2240T1G	MUN5213DW1T1G	MUN5316DW1T1G	MUR130RLG
MUN5111DW1T1G	MUN5213DW1T3G	MUN5330DW1T1G	MUR140G
MUN5111T1G	MUN5213T1G	MUN5333DW1T1G	MUR140RLG

# Multisim 14.0 Education Components

---

MUR1505	MUR1660CTG	MUR3060PTG	MUR550APFRLG
MUR1510	MUR180EG	MUR3060WTG	MUR550PFG
MUR1510G	MUR180ERLG	MUR405	MUR605CT
MUR1515	MUR2020RG	MUR405G	MUR610CT
MUR1515G	MUR2100EG	MUR410	MUR615CT
MUR1520	MUR2100ERLG	MUR4100EG	MUR620CT
MUR1520G	MUR210G	MUR4100ERLG	MUR620CTG
MUR1530	MUR210RLG	MUR410G	MUR805
MUR1540	MUR220G	MUR410RLG	MUR805G
MUR1540G	MUR220RLG	MUR415	MUR810
MUR1550	MUR240G	MUR415G	MUR8100EG
MUR1560	MUR240RLG	MUR415RLG	MUR810G
MUR1560G	MUR2505	MUR420	MUR815
MUR160	MUR2510	MUR420G	MUR815G
MUR1605CT	MUR2515	MUR420RLG	MUR820
MUR160G	MUR2520	MUR440G	MUR820G
MUR160RLG	MUR260G	MUR440RLG	MUR830
MUR1610CT	MUR260RLG	MUR460G	MUR840
MUR1610CTG	MUR3005PT	MUR460RLG	MUR840G
MUR1615CT	MUR3010PT	MUR480EG	MUR850
MUR1615CTG	MUR3015PT	MUR480ERLG	MUR860
MUR1620CT	MUR3020PT	MUR5005	MUR860G
MUR1620CTG	MUR3020PTG	MUR5010	MUR880EG
MUR1620CTRG	MUR3020WTG	MUR5015	MURA105T3G
MUR1640CTG	MUR3040PTG	MUR5020	MURA110T3



# Multisim 14.0 Education Components

---

MURA110T3G	MURD320T4G	MURS110T3	MURS360T3
MURA115T3G	MURD330T4G	MURS110T3G	MURS360T3G
MURA120T3	MURD340T4G	MURS115T3	MURS480ET3G
MURA120T3G	MURD530T4G	MURS115T3G	MUSHROOM_HEAD
MURA130T3G	MURD550PFT4G	MURS120T3	MUX_16TO1
MURA140T3	MURD620CT	MURS120T3G	MUX_2TO1
MURA140T3G	MURD620CTG	MURS140T3	MUX_4TO1
MURA160T3	MURD620CTT4	MURS140T3G	MUX_8TO1
MURA160T3G	MURD620CTT4G	MURS160-E3/52T	MUX_LATCH
MURA205T3G	MURF1560G	MURS160T3	MUX2_1
MURA210T3G	MURF1620CTG	MURS160T3G	MUX2_1_INV
MURA215T3	MURF1660CTG	MURS205T3G	MUX2_1INV_3S
MURA215T3G	MURF550PFG	MURS210T3G	MUX4_1
MURA220T3	MURF860G	MURS220T3	MUX4_1_INVO
MURA220T3G	MURH840CTG	MURS220T3G	MUX8_1
MURA230T3G	MURH860CTG	MURS230T3	MVGSF1N03LT1G
MURA240T3G	MURHB840CTG	MURS230T3G	MVMBF0201NLT1G
MURB1620CTG	MURHB840CTT4	MURS240T3G	myRIO_MXP
MURB1620CTRG	MURHB840CTT4G	MURS310T3	MZ4099
MURB1620CTRT4G	MURHB860CTT4G	MURS320T3	MZ4100
MURB1620CTT4	MURHD560T4G	MURS320T3G	MZ4101
MURB1620CTT4G	MURHD560W1T4G	MURS340T3	MZ4102
MURB1660CTG	MURHF860CTG	MURS340T3G	MZ4103
MURB1660CTT4G	MURHS160T3G	MURS360BT3G	MZ4104
MURD320T4	MURS105T3G	MURS360-E3/57T	MZ4614

# Multisim 14.0 Education Components

---

MZ4615	MZPY100	MZPY6.8	NBRB8H100T4G
MZ4616	MZPY11	MZPY62	NBRD5H100T4G
MZ4617	MZPY12	MZPY68	NBR52H100T3G
MZ4618	MZPY13	MZPY7.5	NC_CONTACT
MZ4619	MZPY15	MZPY75	NC_RELAY_RATED
MZ4620	MZPY16	MZPY8.2	NC7S00_2V
MZ4621	MZPY18	MZPY82	NC7S00_3V
MZ4622	MZPY20	MZPY9.1	NC7S00_4V
MZ4623	MZPY22	MZPY91	NC7S00_5V
MZ4624	MZPY24	N2550-6002RB	NC7S00_6V
MZ4625	MZPY27	NAND13	NC7S02_2V
MZ4626	MZPY3.9	NAND2	NC7S02_3V
MZ4627	MZPY30	NAND2	NC7S02_4V
MZ5520B	MZPY33	NAND3	NC7S02_5V
MZ5521B	MZPY36	NAND3	NC7S02_6V
MZ5522B	MZPY39	NAND4	NC7S04_2V
MZ5523B	MZPY4.3	NAND4	NC7S04_3V
MZ5524B	MZPY4.7	NAND5	NC7S04_4V
MZ5525B	MZPY43	NAND5	NC7S04_5V
MZ5526B	MZPY47	NAND6	NC7S04_6V
MZ5527B	MZPY5.1	NAND6	NC7S08_2V
MZ5528B	MZPY5.6	NAND7	NC7S08_3V
MZ5529B	MZPY51	NAND7	NC7S08_4V
MZ5530B	MZPY56	NAND8	NC7S08_5V
MZPY10	MZPY6.2	NAND8	NC7S08_6V

# Multisim 14.0 Education Components

---

NC7S32_2V	NC7SZ02_2V	NC7SZ32_3V	NCP1011APL130R2 G
NC7S32_3V	NC7SZ02_3V	NC7SZ32_4V	NCP1011ST100T3G
NC7S32_4V	NC7SZ02_4V	NC7SZ32_5V	NCP1011ST130T3G
NC7S32_5V	NC7SZ02_5V	NC7SZ38_2V	NCP1011ST65T3G
NC7S32_6V	NC7SZ04_2V	NC7SZ38_3V	NCP1012AP065G
NC7S86_2V	NC7SZ04_3V	NC7SZ38_4V	NCP1012AP100G
NC7S86_3V	NC7SZ04_4V	NC7SZ38_5V	NCP1012AP133G
NC7S86_4V	NC7SZ04_5V	NC7SZ86_2V	NCP1012APL065R2 G
NC7S86_5V	NC7SZ05_2V	NC7SZ86_3V	NCP1012APL100R2 G
NC7S86_6V	NC7SZ05_3V	NC7SZ86_4V	NCP1012APL130R2 G
NC7ST00_5V	NC7SZ05_4V	NC7SZ86_5V	NCP1012ST100T3G
NC7ST02_5V	NC7SZ05_5V	NC7SZU04_2V	NCP1012ST130T3G
NC7ST04_5V	NC7SZ08_2V	NC7SZU04_3V	NCP1012ST65T3G
NC7ST08_5V	NC7SZ08_3V	NC7SZU04_4V	NCP1013AP065G
NC7ST32_5V	NC7SZ08_4V	NC7SZU04_5V	NCP1013AP100G
NC7ST86_5V	NC7SZ08_5V	NCP1010AP065G	NCP1013AP133G
NC7SU04_2V	NC7SZ125_2V	NCP1010AP100G	NCP1013ST100T3G
NC7SU04_3V	NC7SZ125_3V	NCP1010AP130G	NCP1013ST130T3G
NC7SU04_4V	NC7SZ125_4V	NCP1010ST100T3G	NCP1013ST65T3G
NC7SU04_5V	NC7SZ125_5V	NCP1010ST130T3G	NCP1014AP065G
NC7SU04_6V	NC7SZ126_2V	NCP1011AP065G	NCP1014AP100G
NC7SZ00_2V	NC7SZ126_3V	NCP1011AP100G	NCP1014APL065R2 G
NC7SZ00_3V	NC7SZ126_4V	NCP1011AP130G	NCP1014APL065R2 G
NC7SZ00_4V	NC7SZ126_5V	NCP1011APL065R2 G	
NC7SZ00_5V	NC7SZ32_2V		

# Multisim 14.0 Education Components

---

NCP1014APL100R2G	NCP1052P136G	NCP1117DT15G	NCP1117ST285T3G
NCP1014ST100T3G	NCP1052P44G	NCP1117DT15RKG	NCP1117ST33T3G
NCP1014ST65T3G	NCP1052ST100T3G	NCP1117DT18G	NCP1117ST50T3G
NCP1027P065G	NCP1052ST136T3G	NCP1117DT18RKG	NCP1117STAT3G
NCP1027P100G	NCP1052ST44T3G	NCP1117DT18T5G	NCP1200D100R2G
NCP1028P065G	NCP1053P100G	NCP1117DT20G	NCP1200D40R2G
NCP1028P100G	NCP1053P136G	NCP1117DT20RKG	NCP1200D60R2G
NCP1028PL100R2G	NCP1053P44G	NCP1117DT25G	NCP1200P100G
NCP1030DMR2G	NCP1053ST100T3G	NCP1117DT25RKG	NCP1200P40G
NCP1031DR2G	NCP1053ST136T3G	NCP1117DT25T5G	NCP1200P60G
NCP1031MNTXG	NCP1053ST44T3G	NCP1117DT285G	NCP1203D100R2G
NCP1050P100G	NCP1054P100G	NCP1117DT285RKG	NCP1203D40R2G
NCP1050P136G	NCP1054P136G	NCP1117DT33G	NCP1203D60R2G
NCP1050P44G	NCP1054P44G	NCP1117DT33RKG	NCP1203P100G
NCP1050ST100T3G	NCP1054ST100T3G	NCP1117DT33T5G	NCP1203P40G
NCP1050ST136T3G	NCP1054ST136T3G	NCP1117DT50G	NCP1203P60G
NCP1050ST44T3G	NCP1054ST44T3G	NCP1117DT50RKG	NCP1207ADR2G
NCP1051P100G	NCP1055P100G	NCP1117DTAG	NCP1207APG
NCP1051P136G	NCP1055P136G	NCP1117DTARKG	NCP1207BDR2G
NCP1051P44G	NCP1055P44G	NCP1117DTAT5G	NCP1216AD100R2G
NCP1051ST100T3G	NCP1055ST100T3G	NCP1117ST12T3G	NCP1216AD133R2G
NCP1051ST136T3G	NCP1055ST136T3G	NCP1117ST15T3G	NCP1216AD65R2G
NCP1051ST44T3G	NCP1055ST44T3G	NCP1117ST18T3G	NCP1216AP100G
NCP1052P100G	NCP1117DT12G	NCP1117ST20T3G	NCP1216AP133G
	NCP1117DT12RKG	NCP1117ST25T3G	NCP1216AP65G

# Multisim 14.0 Education Components

---

NCP1216D100R2G	NCP1271D100R2G	NCP2809BMUTXG	NCS2001SQ2T2G
NCP1216D133R2G	NCP1271D65R2G	NCP2890AFCT2G	NCS2200SN1T1G
NCP1216D65R2G	NCP1271P100G	NCP2890DMR2G	NCS2200SN2T1G
NCP1216P100G	NCP1271P65G	NCP4894DMR2G	NCS2200SQ2T2G
NCP1216P133G	NCP1308DR2G	NCP4894FCT1G	NCS2200SQLT1G
NCP1216P65G	NCP1337DR2G	NCP4894MNR2G	NCS2202SN1T1G
NCP1217AD100R2G	NCP1337PG	NCP511SN15T1G	NCS2202SN2T1G
NCP1217AD133R2G	NCP1338DR2G	NCP511SN18T1G	NCS2202SQ1T2G
NCP1217AD65R2G	NCP1351ADR2G	NCP511SN25T1G	NCS2202SQ2T2G
NCP1217AP100G	NCP1351APG	NCP511SN27T1G	NCV1117DT15RKG
NCP1217AP133G	NCP1351BDR2G	NCP511SN28T1G	NCV1117DT18RKG
NCP1217AP65G	NCP1351BPG	NCP511SN30T1G	NCV1117DT18T5G
NCP1217D100R2G	NCP1351CDR2G	NCP511SN33T1G	NCV1117DT20RKG
NCP1217D133R2G	NCP1351CPG	NCP511SN50T1G	NCV1117DT25RKG
NCP1217D65R2G	NCP1351DDR2G	NCP5208DR2G	NCV1117DT33T5G
NCP1217P100G	NCP1351DPG	NCP5217AMNTXG	NCV1117DT50RKG
NCP1217P133G	NCP1377BD1R2G	NCP5355D	NCV1117DTARKG
NCP1217P65G	NCP1377BDR2G	NCP5355DG	NCV1117ST12T3G
NCP1230D100R2G	NCP1377BPG	NCP5355PDR2	NCV1117ST15T3G
NCP1230D133R2G	NCP1377D1R2G	NCP6334BMTAATB G	NCV1117ST18T3G
NCP1230D165R2G	NCP1377DR2G	NCP6334CMTAATB G	NCV1117ST20T3G
NCP1230D65R2G	NCP1377PG		NCV1117ST25T3G
NCP1230P100G	NCP1410DMR2G	NCS2001SN1T1G	NCV1117ST33T3G
NCP1230P133G	NCP2809ADMR2G	NCS2001SN2T1G	NCV1117ST50T3G
NCP1230P65G	NCP2809BDMR2G	NCS2001SQ1T2G	NCV1117STAT3G

# Multisim 14.0 Education Components

---

NCV2001SN2T1G	NDD03N60ZT4G	NDF08N50ZH	NDS9955
NCV2001SQ2T2G	NDD03N80Z-1G	NDF08N60ZG	NDS9956A
NCV2901DR2G	NDD03N80ZT4G	NDF08N60ZH	NDS9958
NCV2901DTBR2G	NDD04N50Z-1G	NDF10N60ZG	NDS9959
NCV2902DR2G	NDD04N50ZT4G	NDF10N60ZH	NDT01N60T1G
NCV2902DTBR2G	NDD04N60Z-1G	NDF10N62ZG	NE5532AI
NCV2903DMR2G	NDD04N60ZT4G	NDF11N50ZG	NE5532AIP
NCV2903DR2G	NDD05N50Z-1G	NDF11N50ZH	NE5532AP
NCV2904DMR2G	NDD05N50ZT4G	NDF9406	NE5532IP
NCV2904DR2G	NDD60N360U1-1G	NDF9407	NE5532P
NCV33063AVDR2G	NDD60N360U1-35G	NDF9409	NE5534AD
NCV33074ADTBR2 G	NDD60N360U1T4G	NDF9410	NE5534AP
NCV33074DR2G	NDF02N60ZG	NDS8852H	NE5534D
NCV33272ADR2G	NDF02N60ZH	NDS8858H	NE5534P
NCV833DR2G	NDF03N60ZG	NDS8936	NET_10
NDD01N60-1G	NDF03N60ZH	NDS8947	NET_12
NDD01N60T4G	NDF04N60ZG	NDS9936	NET_14
NDD02N40-1G	NDF04N60ZH	NDS9942	NET_16
NDD02N40T4G	NDF04N62ZG	NDS9943	NET_18
NDD02N60Z-1G	NDF05N50ZG	NDS9947	NET_2
NDD02N60ZT4G	NDF05N50ZH	NDS9948	NET_20
NDD03N50Z-1G	NDF06N60ZG	NDS9952	NET_3
NDD03N50ZT4G	NDF06N60ZH	NDS9952A	NET_4
NDD03N60Z-1G	NDF06N62ZG	NDS9953	NET_6
	NDF08N50ZG	NDS9953A	NET_8

# Multisim 14.0 Education Components

---

NF5101	NI_cRIO_INTERFAC E_ID	NI_sbRIO_P5_CON N	NIF9N05CLT3G
NF5102			NI-GPIB-ENET/100
NF5103	NI_cRIO_INTERFAC E_PARALLEL	NI_sbRIO_P5_PORT S	NI-GPIB-ENET/1000
NF5301	NI_cRIO_INTERFAC E_SPI	NI_VHDCI_68_RA	NI-GPIB-PCII/IIA
NGB18N40CLBT4G		NI_VHDCI_68_V	NI-GPIB-RS232
NGB8207NT4G	NI_cRIO_INTERFAC E_USER	NI-78xxR_RDIO	NI-GPIB-RS485/422
NGD15N41CLT4G	NI_cRIO_SCREWTE RM10	NI-9683_AI	NI-GPIB-USB-HS
NGD18N40CLBT4G		NI-9683_AIO	NI-myDAQ
NGD8201NT4G	NI_MyDAQ_Rail_llef t	NI-9683_DI	NI-PCI-6011E
NGTB15N60S1EG		NI-9683_DO	NI-PCI-6013
NGTB50N60FLWG	NI_MyDAQ_top	NI-	NI-PCI-6014
NHPJ08S600G	NI_sbRIO_J5_CONN	9683_HALFBRIDGE_ DO	NI-PCI-6023E
NHPJ15S600G	NI_sbRIO_J6_CONN		NI-PCI-6024E
NHPV08S600G	NI_sbRIO_J7_CONN	NI-9683_LVTTL	NI-PCI-6030E
NHPV15S600G	NI_sbRIO_J7_PORT S	NI-AT-GPIB/TNT	NI-PCI-6032E
NI_2VHDCI_68_68_ RA	NI_sbRIO_P2_CON N	NID9N05CLT4G	NI-PCI-6034E
NI_50MIL_68_RA		NI-DAQCard-6024E	NI-PCI-6035E
NI_50MIL_68_V	NI_sbRIO_P2_PORT S	NI-DAQCard-6036E	NI-PCI-6036E
NI_cRIO_4LED_RA	NI_sbRIO_P3_CON N	NI-DAQCard-6062E	NI-PCI-6040E
NI_cRIO_BNC	NI_sbRIO_P3_PORT S	NI-DAQPad- 6015(Mass.Term.)	NI-PCI-6052E
NI_cRIO_DSUB25M		NI-DAQPad-6020E	NI-PCI-6070E
NI_cRIO_DSUB37M	NI_sbRIO_P4_CON N	NI-DAQPad-6052E	NI-PCI-6110
NI_cRIO_INTERFAC E_GENERIC	NI_sbRIO_P4_PORT S	NI-ExpressCard- GPIB	NI-PCI-6111
		NIF9N05CLT1G	NI-PCI-6115
			NI-PCI-6120

# Multisim 14.0 Education Components

---

NI-PCI-6122	NI-PCI-6289	NI-PCle-7852R_RMIO	NI-PXI-6229
NI-PCI-6123	NI-PCI-7811R	NI-PCle-GPIB	NI-PXI-6230
NI-PCI-6132	NI-PCI-7813R	NI-PCle-GPIB/LP	NI-PXI-6232
NI-PCI-6133	NI-PCI-7830R_RMIO	NI-PCle-GPIB+	NI-PXI-6233
NI-PCI-6143	NI-PCI-7831R_RMIO	NI-PCle-GPIB+/LP	NI-PXI-6236
NI-PCI-6154	NI-PCI-7833R_RMIO	NI-PCI-GPIB	NI-PXI-6238
NI-PCI-6220	NI-PCI-8232	NI-PCI-GPIB/LP	NI-PXI-6239
NI-PCI-6221	NI-PCle-6251	NI-PCI-GPIB+	NI-PXI-6250
NI-PCI-6221(37-Pin)	NI-PCle-6259	NI-PCMCIA-GPIB	NI-PXI-6251
NI-PCI-6224	NI-PCle-6320	NI-PMC-GPIB	NI-PXI-6254
NI-PCI-6225	NI-PCle-6321	NI-PXI-6030E	NI-PXI-6255
NI-PCI-6229	NI-PCle-6323	NI-PXI-6040E	NI-PXI-6259
NI-PCI-6230	NI-PCle-6341	NI-PXI-6052E	NI-PXI-6280
NI-PCI-6232	NI-PCle-6343	NI-PXI-6070E	NI-PXI-6281
NI-PCI-6233	NI-PCle-6351	NI-PXI-6115	NI-PXI-6284
NI-PCI-6236	NI-PCle-6353	NI-PXI-6120	NI-PXI-6289
NI-PCI-6238	NI-PCle-6361	NI-PXI-6122	NI-PXI-7811R
NI-PCI-6239	NI-PCle-6363	NI-PXI-6123	NI-PXI-7813R
NI-PCI-6250	NI-PCle-7841R_RMIO	NI-PXI-6132	NI-PXI-7830R_RMIO
NI-PCI-6254	NI-PCle-7842R_RMIO	NI-PXI-6133	NI-PXI-7831R_RMIO
NI-PCI-6255	NI-PCle-7851R_RMIO	NI-PXI-6143	NI-PXI-7833R_RMIO
NI-PCI-6259		NI-PXI-6221	NI-PXI-7841R_RMIO
NI-PCI-6280		NI-PXI-6224	NI-PXI-7842R_RMIO
NI-PCI-6281		NI-PXI-6225	NI-PXI-7851R_RMIO
NI-PCI-6284			NI-PXI-7852R_RMIO



# Multisim 14.0 Education Components

---

NI-PXI-7853R_RMIO	NI-SCXI-1128_2-Wire	NI-USB-78xxR_DIO	NJM064D
NI-PXI-7854R_RMIO		NJD1718T4G	NJM064M
NI-PXI-8232	NI-SCXI-1128_4-Wire	NJD2873T4G	NJM064V
NI-PXIe-6124	NI-SCXI-	NJD35N04G	NJM072BD
NI-PXIe-6341	1128_Independent	NJD35N04T4G	NJM072BL
NI-PXIe-6356	NI-SCXI-	NJL0281D	NJM072BM
NI-PXIe-6358	1128_Matrix	NJL0281DG	NJM072BV
NI-PXIe-6361	NI-SCXI-1160	NJL0302D	NJM072D
NI-PXIe-6363	NI-SCXI-1163R	NJL0302DG	NJM072L
NI-PXIe-6366	NI-USB-	NJL1302DG	NJM072M
NI-PXIe-6368	6212(Mass.Term.)	NJL3281DG	NJM074D
NI-PXI-GPIB	NI-USB-	NJL4281D	NJM074M
NI-sbRIO-9605	6216(Mass.Term.)	NJL4281DG	NJM074V
NI-sbRIO-9606	NI-USB-	NJL4302D	NJM082BD
NI-sbRIO-9651	6251(Mass.Term.)	NJL4302DG	NJM082BL
NI-SCXI-1127_1-Wire	NI-USB-	NJM022BD	NJM082BM
	6255(Mass.Term.)	NJM022BL	NJM082BV
NI-SCXI-1127_2-Wire	NI-USB-	NJM022BM	NJM082D
	6259(Mass.Term.)	NJM022D	NJM082L
NI-SCXI-1127_4-Wire	NI-USB-	NJM022L	NJM082V
	6281(Mass.Term.)	NJM022M	NJM084D
NI-SCXI-	NI-USB-	NJM062D	NJM084M
1127_Independent	6289(Mass.Term.)	NJM062L	NJM084V
NI-SCXI-	NI-USB-7845R_MIO	NJM062M	NJM13600D
1127_Matrix	NI-USB-7846R_MIO	NJM062V	NJM13600M
NI-SCXI-1128_1-Wire	NI-USB-7855R_MIO		
	NI-USB-7856R_MIO		

# Multisim 14.0 Education Components

---

NJM13700D	NJM2100M	NJM324D	NJM4580D
NJM13700M	NJM2100V	NJM324M	NJM4580E
NJM1458D	NJM2107F	NJM3403AD	NJM4580L
NJM1458M	NJM2114D	NJM3403AM	NJM4741D
NJM2041D	NJM2114L	NJM3403AV	NJM4741M
NJM2041L	NJM2115D	NJM3404AD	NJM5532D
NJM2041M	NJM2115L	NJM3404AL	NJM5532L
NJM2043D	NJM2115M	NJM3404AM	NJM5532M
NJM2043L	NJM2120D	NJM3414D	NJM5534D
NJM2043M	NJM2120L	NJM3414L	NJM5534M
NJM2058D	NJM2120M	NJM3414M	NJM741D
NJM2058M	NJM2121D	NJM3415D	NJM741E
NJM2059D	NJM2121L	NJM3415L	NJM741M
NJM2059M	NJM2121M	NJM3415M	NJMOP-07D
NJM2060D	NJM2900M	NJM3416V	NJMOP-07M
NJM2060M	NJM2900N	NJM353D	NJT4030PT1G
NJM2068D	NJM2902M	NJM353M	NJT4030PT3G
NJM2068L	NJM2902N	NJM3900M	NJT4031NT1G
NJM2068M	NJM2902V	NJM3900N	NJT4031NT3G
NJM2082D	NJM2904D	NJM4250D	NJV4030PT1G
NJM2082L	NJM2904L	NJM4250M	NJV4030PT3G
NJM2082M	NJM2904M	NJM4565D	NJV4031NT1G
NJM2097M	NJM2904V	NJM4565L	NJV4031NT3G
NJM2100D	NJM318D	NJM4565M	NJVMJB41CT4G
NJM2100L	NJM318M	NJM4565V	NJVMJB42CT4G

# Multisim 14.0 Education Components

---

NJVMJB44H11T4G	NJVNJD35N04G	NOR3	NRVB10100MFST1G
NJVMJB45H11T4G	NJVNJD35N04T4G	NOR3	NRVB10100MFST3G
NJVMJD112T4G	NJW0281G	NOR4	NRVB1045MFST1G
NJVMJD117T4G	NJW0302G	NOR4	NRVB1045MFST3G
NJVMJD210T4G	NJW1302G	NOR5	NRVB120ESFT1G
NJVMJD243T4G	NJW21193G	NOR5	NRVB120ESFT3G
NJVMJD253T4G	NJW21194G	NOR6	NRVB120LSFT1G
NJVMJD2955T4G	NJW3281G	NOR6	NRVB1240MFST1G
NJVMJD3055T4G	NJX1675PDR2G	NOR7	NRVB1240MFST3G
NJVMJD31T4G	NLT_VIRTUAL	NOR7	NRVB130T1G
NJVMJD32CG	NMOSFET_Thermal	NOR8	NRVB140ESFT1G
NJVMJD32CT4G	NO_CONTACT	NOR8	NRVB140ESFT3G
NJVMJD32T4G	NO_RELAY_RATED	NOT	NRVB140SFT1G
NJVMJD350T4G	NON_IDEAL_BATTERY	NPD5564	NRVB140SFT3G
NJVMJD42CRLG	NON_IDEAL_CAPACITOR	NPD5565	NRVB1H100SFT3G
NJVMJD42CT4G	NON_IDEAL_INDUC	NPD5566	NRVB2045EMFST1G
NJVMJD44E3T4G	NON_IDEAL_INDUC	NPD8301	NRVB2045EMFST3G
NJVMJD44H11G	NON_IDEAL_RESISTOR	NPD8303	NRVB2H100SFT3G
NJVMJD44H11RLG	NONC_RELAY_RATE	NRVA4004T3G	NRVB30H100MFST1G
NJVMJD44H11T4G	D	NRVB0530T1G	NRVB30H100MFST3G
NJVMJD45H11RLG	NONLINEAR_DEPEN	NRVB0530T3G	NRVB440MFST1G
NJVMJD45H11T4G	DENT	NRVB0540T1G	
NJVMJD50T4G		NRVB0540T3G	
NJVMJD6039T4G	NOR2	NRVB10100G	
NJVNJD2873T4G	NOR2		

# Multisim 14.0 Education Components

---

NRVB440MFST3G	NRVBB2060CTT4G	NRVBM140T1G	NSB9435T1G
NRVB440MFSWFT1G	NRVBB20H100CTT4G	NRVBM140T3G	NSBA114EDP6T5G
NRVB440MFSWFT3G	NRVBB2535CTLG	NRVBS2040LT3G	NSBA114EDXV6T1G
NRVB460MFST1G	NRVBB2535CTLT4G	NRVBS240LT3G	NSBA114EF3T5G
NRVB460MFST3G	NRVBB3030CTLG	NRVBS260T3G	NSBA114TDP6T5G
NRVB5100MFST1G	NRVBB3030CTLT4G	NRVBS3100T3G	NSBA114TF3T5G
NRVB5100MFST3G	NRVBB30H60CTT4G	NRVBS3200T3G	NSBA114YDP6T5G
NRVB540MFST1G	NRVBB4030T4G	NRVBS3201T3G	NSBA114YDXV6T1G
NRVB540MFST3G	NRVBB41H100CTT4G	NRVBS330T3G	NSBA115EDXV6T1G
NRVB560MFST1G	NRVBB41H100CTT4G	NRVBS360T3G	NSBA115TDP6T5G
NRVB560MFST3G	NRVBBS20100CTT4G	NRVBS4201T3G	NSBA115TF3T5G
NRVB5H100MFST1G	NRVBD1035CTLT4G	NRVBS540T3G	NSBA123EF3T5G
NRVB5H100MFST3G	NRVBD640CTG	NRVS1504T3G	NSBA123JDP6T5G
NRVB8H100MFST1G	NRVBD640CTT4G	NRVUB1620CTRT4G	NSBA123JDXV6T5G
NRVB8H100MFST3G	NRVBD650CTT4G	NRVUB1620CTT4G	NSBA123JF3T5G
NRVBA130LT3G	NRVBD660CTG	NRVUB1660CTT4G	NSBA123TDP6T5G
NRVBA160T3G	NRVBD660CTT4G	NRVUD550PFT4G	NSBA123TF3T5G
NRVBA1H100T3G	NRVBM110ET1G	NRVUD620CTG	NSBA124EDP6T5G
NRVBA210LT3G	NRVBM110LT1G	NRVUD620CTT4G	NSBA124EF3T5G
NRVBA2H100T3G	NRVBM110LT3G	NRVUS230T3G	NSBA124XF3T5G
NRVBA340T3G	NRVBM110LT3G	NRVUS240T3G	NSBA143EDP6T5G
NRVBB1060T4G	NRVBM120ET1G	NSA5.0AT3G	NSBA143EF3T5G
NRVBB20100CTT4G	NRVBM120ET3G	NSB12ANT3G	NSBA143TF3T5G
	NRVBM130LT1G	NSB4904DW1T1G	NSBA143ZDP6T5G
	NRVBM130LT3G	NSB8MT-E3/81	NSBA143ZF3T5G

# Multisim 14.0 Education Components

---

NSBA144EDP6T5G	NSBC114YPDXV6T5G	NSBC143ZDXV6T1G	NSI45025ZT1G
NSBA144EDXV6T1G		NSBC143ZF3T5G	NSI45030AT1G
NSBA144EF3T5G	NSBC115EDXV6T1G	NSBC143ZPDP6T5G	NSI45030AZT1G
NSBA144TF3T5G	NSBC115TDP6T5G	NSBC143ZPDXV6T1G	NSI45030T1G
NSBA144WDP6T5G	NSBC115TF3T5G		NSI45030ZT1G
NSBA144WF3T5G	NSBC115TPDP6T5G	NSBC144EDP6T5G	NSI45035JZT1G
NSBC113EF3T5G	NSBC123EF3T5G	NSBC144EDXV6T1G	NSI45060DDT4G
NSBC114EDP6T5G	NSBC123JDP6T5G	NSBC144EDXV6T5G	NSI45090DDT4G
NSBC114EDXV6T1G	NSBC123JF3T5G	NSBC144EF3T5G	NSI45090JDT4G
NSBC114EDXV6T5G	NSBC123JPDP6T5G	NSBC144EPDP6T5G	NSI50010YT1G
NSBC114EF3T5G	NSBC123JPDXV6T1G	NSBC144EPDXV6T1G	NSI50150ADT4G
NSBC114EPDP6T5G			
NSBC114EPDXV6T1G	NSBC123TDP6T5G	NSBC144TF3T5G	NSI50350ADT4G
	NSBC123TF3T5G	NSBC144WDP6T5G	NSI50350AST3G
NSBC114EPDXV6T5G	NSBC124EDP6T5G	NSBC144WF3T5G	NSIC2020BT3G
	NSBC124EDXV6T1G	NSD16F3T5G	NSIC2030BT3G
NSBC114TDP6T5G	NSBC124EF3T5G	NSD914F3T5G	NSIC2050BT3G
NSBC114TDXV6T1G	NSBC124EPDXV6T1G	NSDEMP11XV6T1G	NSL12AWT1G
NSBC114TF3T5G		NSDEMP11XV6T5G	NSM80100MT1G
NSBC114YDP6T5G	NSBC124XF3T5G	NSI45015WT1G	NSM80101MT1G
NSBC114YDXV6T1G	NSBC143EDP6T5G	NSI45020AT1G	NSR0130P2T5G
NSBC114YDXV6T5G	NSBC143EF3T5G	NSI45020JZT1G	NSR0140P2T5G
NSBC114YF3T5G	NSBC143TF3T5G	NSI45020T1G	NSR01F30MXT5G
NSBC114YPDP6T5G	NSBC143TPDXV6T1G	NSI45025AT1G	NSR01F30NXT5G
NSBC114YPDXV6T1G		NSI45025AZT1G	NSR01L30MXT5G
	NSBC143ZDP6T5G	NSI45025T1G	NSR01L30NXT5G

# Multisim 14.0 Education Components

---

NSR0230P2T5G	NSR30CM3T5G	NSS30100LT1G	NST3904DXV6T5G
NSR0240HT1G	NSRLV20MW2T1G	NSS30101LT1G	NST3904F3T5G
NSR0240P2T5G	NSS12100M3T5G	NSS30201MR6T1G	NST3906DXV6T1G
NSR0240V2T1G	NSS12100UW3TCG	NSS35200CF8T1G	NST3906F3T5G
NSR02F30NXT5G	NSS12100XV6T1G	NSS35200MR6T1G	NST3946DXV6T1G
NSR02L30NXT5G	NSS12200LT1G	NSS40200LT1G	NST3946DXV6T5G
NSR0320MW2T1G	NSS12200WT1G	NSS40200UW6T1G	NST846BF3T5G
NSR0320MW2T3G	NSS12201LT1G	NSS40201LT1G	NST847BF3T5G
NSR0320XV6T1G	NSS12500UW3T2G	NSS40300DDR2G	NST848BF3T5G
NSR0320XV6T5G	NSS12501UW3T2G	NSS40300MDR2G	NST856BF3T5G
NSR0340HT1G	NSS12601CF8T1G	NSS40300MZ4T1G	NST857BF3T5G
NSR0340P2T5G	NSS1C200LT1G	NSS40301MDR2G	NSTB1005DXV5T1G
NSR0340V2T1G	NSS1C200MZ4T1G	NSS40301MZ4T1G	NSTR4501NT1G
NSR0520V2T1G	NSS1C200MZ4T3G	NSS40302PDR2G	NSV1C300ET4G
NSR05F20NXT5G	NSS1C201LT1G	NSS40500UW3T2G	NSV1C301ET4G
NSR05F30NXT5G	NSS1C201MZ4T1G	NSS40501UW3T2G	NSV20200LT1G
NSR05F40NXT5G	NSS1C201MZ4T3G	NSS40600CF8T1G	NSV20201LT1G
NSR0620P2T5G	NSS1C300ET4G	NSS40601CF8T1G	NSV40200LT1G
NSR1020MW2T1G	NSS1C301ET4G	NSS60200LT1G	NSV40201LT1G
NSR1020MW2T3G	NSS20200LT1G	NSS60201LT1G	NSV40300MDR2G
NSR10F20NXT5G	NSS20201LT1G	NSS60600MZ4T1G	NSV40300MZ4T1G
NSR10F30NXT5G	NSS20300MR6T1G	NSS60601MZ4T1G	NSV40301MZ4T1G
NSR10F40NXT5G	NSS20500UW3T2G	NST30010MXV6T1 G	NSV60600MZ4T1G
NSR20F20NXT5G	NSS20501UW3T2G	NST3904DXV6T1G	NSV60600MZ4T3G
NSR20F30NXT5G	NSS20601CF8T1G		NSV60601MZ4T1G

# Multisim 14.0 Education Components

---

NSV60601MZ4T3G	NSVMUN5212DW1 T1G	NTB6412ANG	NTD3055L104-1G
NSV9435T1G		NTB6412ANT4G	NTD3055L104G
NSVB123JPD XV6T1 G	NSVMUN5333DW1 T1G	NTB6413ANG	NTD3055L104T4G
NSVB143ZPD XV6T1 G	NSVMUN5334DW1 T1G	NTB6413ANT4G	NTD3055L170T4G
NSVB144EPD XV6T1 G	NSVT30010MXV6T1 G	NTB75N03L09T4G	NTD32N06LT4G
NSVBA114YD XV6T1 G	NSVT3904DXV6T1G	NTB75N06T4G	NTD40N03RT4G
NSVBAT54WT1G	NTA4001NT1G	NTBV5605T4G	NTD4302T4G
NSVBAV70TT1G	NTA4151PT1G	NTD110N02RT4G	NTD4804NT4G
NSVBAV70TT3G	NTA4153NT1G	NTD12N10-1G	NTD4805N-1G
NSVBC124ED XV6T1 G	NTA7002NT1G	NTD12N10T4G	NTD4805NT4G
NSVBCP69T1G	NTB25P06T4G	NTD14N03RT4G	NTD4806N-35G
NSVMMBD353LT1G	NTB30N06LT4G	NTD18N06LT4G	NTD4806NT4G
NSVMMBT589LT1G	NTB30N20T4G	NTD18N06T4G	NTD4808N-1G
NSVMMBTH10LT1G	NTB45N06LT4G	NTD20N03L27T4G	NTD4808NT4G
NSVMMUN2132LT1 G	NTB45N06T4G	NTD20N06T4G	NTD4809N-35G
NSVMMUN2232LT1 G	NTB5404NT4G	NTD20P06LG	NTD4809NH-1G
NSVMUN2212T1G	NTB5405NT4G	NTD20P06LT4G	NTD4809NH-35G
NSVMUN2233T1G	NTB5605PT4G	NTD24N06LT4G	NTD4809NHT4G
NSVMUN5131T1G	NTB60N06T4G	NTD24N06T4G	NTD4809NT4G
NSVMUN5132T1G	NTB6410ANG	NTD2955-1G	NTD4810N-35G
	NTB6410ANT4G	NTD2955G	NTD4810NT4G
	NTB6411ANG	NTD2955T4G	NTD4813N-35G
	NTB6411ANT4G	NTD3055-094-1G	NTD4813NH-1G
		NTD3055-094T4G	NTD4813NH-35G
		NTD3055-150T4G	NTD4813NHT4G

# Multisim 14.0 Education Components

---

NTD4813NT4G	NTD4909N-35G	NTD5802NT4G	NTF2955T1G
NTD4815N-35G	NTD4909NT4G	NTD5803NT4G	NTF3055-100T1G
NTD4815NT4G	NTD4910N-1G	NTD5804NT4G	NTF3055-100T3G
NTD4855NT4G	NTD4910N-35G	NTD5805NT4G	NTF3055L108T1G
NTD4856NT4G	NTD4910NT4G	NTD5806NT4G	NTF3055L175T1G
NTD4857NT4G	NTD4913N-1G	NTD5807NT4G	NTF5P03T3G
NTD4858N-35G	NTD4913N-35G	NTD5865NL-1G	NTF6P02T3G
NTD4858NT4G	NTD4913NT4G	NTD5865NLT4G	NTGD1100LT1G
NTD4860N-35G	NTD4960N-1G	NTD5867NL-1G	NTGD3149CT1G
NTD4860NT4G	NTD4960N-35G	NTD5867NLT4G	NTGD4161PT1G
NTD4863N-35G	NTD4960NT4G	NTD6414AN-1G	NTGD4167CT1G
NTD4863NAT4G	NTD4963N-1G	NTD6414ANT4G	NTGS3130NT1G
NTD4863NT4G	NTD4963N-35G	NTD6415AN-1G	NTGS3136PT1G
NTD4863NT4H	NTD4963NT4G	NTD6415ANLT4G	NTGS3441PT1G
NTD4865NT4G	NTD4965N-1G	NTD6415ANT4G	NTGS3441T1G
NTD4904N-1G	NTD4965N-35G	NTD6416AN-1G	NTGS3443T1G
NTD4904N-35G	NTD4965NT4G	NTD6416ANL-1G	NTGS3446T1G
NTD4904NT4G	NTD4969N-1G	NTD6416ANLT4G	NTGS4111PT1G
NTD4905N-1G	NTD4969N-35G	NTD6416ANT4G	NTGS4141NT1G
NTD4905N-35G	NTD4969NT4G	NTD6600NT4G	NTGS5120PT1G
NTD4905NT4G	NTD4970N-1G	NTD70N03R-1G	NTHC5513T1G
NTD4906N-1G	NTD4970N-35G	NTD70N03RT4G	NTHD2102PT1G
NTD4906N-35G	NTD4970NT4G	NTDV20N06T4G	NTHD3100CT1G
NTD4906NT4G	NTD5406NT4G	NTE4151PT1G	NTHD3101FT1G
NTD4909N-1G	NTD5407NT4G	NTE4153NT1G	NTHD3102CT1G



# Multisim 14.0 Education Components

---

NTHD3133PFT1G	NTK3043NT1G	NTLUS3A90PZTAG	NTMFS4833NT1G
NTHD4102PT1G	NTK3134NT1G	NTLUS3A90PZTBG	NTMFS4833NT3G
NTHD4502NT1G	NTK3134NT5G	NTMD3P03R2G	NTMFS4834NT1G
NTHD4508NT1G	NTK3139PT1G	NTMD4184PFR2G	NTMFS4835NT1G
NTHD4P02FT1G	NTK3139PT5G	NTMD4820NR2G	NTMFS4836NT1G
NTHS4101PT1G	NTK3142PT1G	NTMD4840NR2G	NTMFS4837NHT1G
NTHS4166NT1G	NTLGD3502NT2G	NTMD4884NFR2G	NTMFS4839NHT1G
NTHS5404T1G	NTLGF3402PT2G	NTMD4N03R2G	NTMFS4841NHT1G
NTHS5441T1G	NTLJD3115PT1G	NTMD5836NLR2G	NTMFS4841NT1G
NTHS5443T1G	NTLJD3119CTAG	NTMD5838NLR2G	NTMFS4845NT1G
NTJD1155LT1G	NTLJD3119CTBG	NTMD6N02R2G	NTMFS4846NT1G
NTJD4001NT1G	NTLJD4116NT1G	NTMD6N04R2G	NTMFS4847NAT1G
NTJD4105CT1G	NTLJF3117PT1G	NTMD6P02R2G	NTMFS4847NAT3G
NTJD4105CT2G	NTLJF4156NT1G	NTMFD4901NFT1G	NTMFS4847NT1G
NTJD4152PT1G	NTLJF4156NTAG	NTMFD4901NFT3G	NTMFS4851NT1G
NTJD4158CT1G	NTLJS2103PTBG	NTMFD4902NFT1G	NTMFS4852NT1G
NTJD4158CT2G	NTLJS3113PT1G	NTMFD4902NFT3G	NTMFS4852NT3G
NTJD4401NT1G	NTLJS3113PTAG	NTMFS4108NT1G	NTMFS4897NFT1G
NTJD5121NT1G	NTLJS4114NT1G	NTMFS4119NT1G	NTMFS4897NFT3G
NTJD5121NT2G	NTLLD4901NFTWG	NTMFS4744NT1G	NTMFS4898NFT1G
NTJS3151PT1G	NTLUD3A260PZTAG	NTMFS4821NT1G	NTMFS4898NFT3G
NTJS3157NT1G	NTLUD3A260PZTBG	NTMFS4823NT1G	NTMFS4899NFT1G
NTJS4151PT1G	NTLUF4189NZTAG	NTMFS4823NT3G	NTMFS4899NFT3G
NTJS4160NT1G	NTLUS3A40PZTAG	NTMFS4825NFET1G	NTMFS4921NT1G
NTJS4405NT1G	NTLUS3A40PZTBG	NTMFS4825NFET3G	NTMFS4921NT3G

# Multisim 14.0 Education Components

---

NTMFS4922NET1G	NTMFS4939NT3G	NTMS4917NR2G	NTR4502PT3G
NTMFS4922NET3G	NTMFS4941NT1G	NTMS4920NR2G	NTR4503NT1G
NTMFS4923NET1G	NTMFS4941NT3G	NTMS4935NR2G	NTS2101PT1G
NTMFS4923NET3G	NTMFS4943NT1G	NTMS4937NR2G	NTS4001NT1G
NTMFS4925NET1G	NTMFS4943NT3G	NTMS4939NR2G	NTS4101PT1G
NTMFS4925NET3G	NTMFS4945NT1G	NTMS5835NLR2G	NTS4173PT1G
NTMFS4925NT1G	NTMFS4983NFT1G	NTMS5838NLR2G	NTS4409NT1G
NTMFS4925NT3G	NTMFS4983NFT3G	NTMS5P02R2G	NTSB20100CT-1G
NTMFS4926NET1G	NTMFS4985NFT1G	NTNS3A65PZT5G	NTSB20U100CT-1G
NTMFS4926NET3G	NTMFS4985NFT3G	NTNUS3171PZT5G	NTSB30100CT-1G
NTMFS4926NT1G	NTMFS5830NLT1G	NTP2955G	NTSB30100S-1G
NTMFS4926NT3G	NTMFS5832NLT1G	NTP35N15G	NTSB30U100CT-1G
NTMFS4927NT1G	NTMS10P02R2G	NTR0202PLT1G	NTSJ20100CTG
NTMFS4927NT3G	NTMS4176PR2G	NTR1P02LT1G	NTSJ2080CTG
NTMFS4931NT1G	NTMS4177PR2G	NTR1P02LT3G	NTSJ20U100CTG
NTMFS4931NT3G	NTMS4503NR2G	NTR2101PT1G	NTSJ30100CTG
NTMFS4934NT1G	NTMS4800NR2G	NTR3161NT1G	NTSJ3080CTG
NTMFS4934NT3G	NTMS4801NR2G	NTR3162PT1G	NTSJ30U80CTG
NTMFS4935NT1G	NTMS4802NR2G	NTR4003NT1G	NTST20100CTG
NTMFS4935NT3G	NTMS4807NR2G	NTR4003NT3G	NTST20120CTG
NTMFS4936NT1G	NTMS4816NR2G	NTR4101PT1G	NTST20U100CTG
NTMFS4936NT3G	NTMS4840NR2G	NTR4170NT1G	NTST30100CTG
NTMFS4937NT1G	NTMS4872NR2G	NTR4171PT1G	NTST30100CTH
NTMFS4937NT3G	NTMS4873NFR2G	NTR4501NT1G	NTST30100SG
NTMFS4939NT1G	NTMS4916NR2G	NTR4502PT1G	NTST30120CTG

# Multisim 14.0 Education Components

---

NTST30U100CTG	NTTFS4941NTAG	NTZD3152PT1G	NUF4001MUT2G
NTST30U100CTH	NTTFS4941NTWG	NTZD3154NT1G	NUF4220MNT1G
NTST40120CTG	NTTFS4943NTAG	NTZD3154NT2G	NUF4401MNT1G
NTST40120CTH	NTTFS4945NTAG	NTZD3154NT5G	NUF4403MNT1G
NTSV20100CTG	NTTFS4985NFTAG	NTZD3155CT1G	NUF6001MUT2G
NTSV20120CTG	NTTFS4985NFTWG	NTZD3155CT2G	NUF6105FCT1G
NTSV20U100CTG	NTTFS4C05NTAG	NTZD3155CT5G	NUF6401MNT1G
NTSV30100CTG	NTTFS4C05NTWG	NTZD5110NT1G	NUF6402MNT1G
NTSV30120CTG	NTTFS4C06NTAG	NTZS3151PT1G	NUF8001MUT2G
NTTD4401FR2G	NTTFS4C06NTWG	NUD3105DMT1G	NUF8401MNT4G
NTTFS4800NTAG	NTTFS4C08NTAG	NUD3105LT1G	NUF8402MNT4G
NTTFS4821NTAG	NTTFS4C08NTWG	NUD3112DMT1G	NUF8410MNT4G
NTTFS4821NTWG	NTTFS4C10NTAG	NUD3112LT1G	NUF9002FCT1G
NTTFS4823NTAG	NTTFS4C10NTWG	NUD3124DMT1G	NUMERIC_KEYPAD_ 4X4
NTTFS4823NTWG	NTTFS4C13NTAG	NUD3124LT1G	NUMERIC_KEYPAD_ 4X5
NTTFS4824NTAG	NTTFS4C13NTWG	NUD3160DMT1G	
NTTFS4840NTAG	NTTFS5811NLTAG	NUD3160LT1G	NUP1105LT1G
NTTFS4929NTAG	NTTFS5811NLTWG	NUF2042XV6T1G	NUP1301
NTTFS4929NTWG	NTTFS5820NLTAG	NUF2114MNT1G	NUP1301ML3T1G
NTTFS4932NTAG	NTTFS5820NLTWG	NUF2116MNT1G	NUP1301U
NTTFS4932NTWG	NTUD3127CT5G	NUF2221W1T2G	NUP2105LT1G
NTTFS4937NTAG	NTUD3128NT5G	NUF2230XV6T1G	NUP2202W1T2G
NTTFS4937NTWG	NTUD3169CZT5G	NUF2450MUT2G	NUP4102XV6T1G
NTTFS4939NTAG	NTUD3170NZT5G	NUF3101FCT1G	NUP4103FCT1G
NTTFS4939NTWG	NTUD3171PZT5G	NUF3102MUTAG	NUP4201DR2G

# Multisim 14.0 Education Components

---

NUP4201MR6T1G	NVMFD5485NLT3G	NVMFS5844NLT1G	NX3008NBKS
NUP4202W1T2G	NVMFD5485NLWFT 1G	NVMFS5844NLT3G	NX3008NBKT
NUP4301MR6T1G	NVMFD5485NLWFT 3G	NVMFS5885NLT1G	NX3008NBKV
NUP4302MR6T1G	NVMFD5489NLT1G	NVMFS5885NLT3G	NX3008NBKW
NUP4304MR6T1G	NVMFD5489NLT3G	NVMS4816NR2G	NX3008PBK
NUP45V6P5T5G	NVMFD5489NLWFT 1G	NVR5198NLT1G	NX3008PBKMB
NUS3116MTR2G	NVMFD5489NLWFT 3G	NVR5198NLT3G	NX3008PBKS
NVB6413ANT4G	NVMFD5489NLWFT 1G	NVTA7002NT1G	NX3008PBKT
NVD4804NT4G	NVMFD5852NLT1G	NVTFS4824NTAG	NX3008PBKV
NVD5117PLT4G	NVMFD5852NLWFT 1G	NVTFS4824NTWG	NX3008PBKW
NVD5802NT4G	NVMFD5873NLT1G	NVTFS4C25NTAG	NX7002AK
NVD5807NT4G	NVMFD5873NLWFT 1G	NVTFS5116PLTAG	NX7002AKS
NVD5865NLT4G	NVMFD5877NLT1G	NVTFS5116PLTWG	NX7002AKW
NVD5890NT4G	NVMFD5877NLWFT 1G	NVTFS5124PLTAG	NXP3875G
NVD6415ANLT4G	NVMFD5877NLT3G	NVTFS5124PLTWG	NXP3875Y
NVD6824NLT4G	NVMFD5877NLWFT 1G	NVTFS5826NLTAG	NZ9F2V4ST5G
NVDD5894NLT4G	NVMFD5877NLT3G	NVTFS5826NLTWG	NZ9F2V4T5G
NVF2955T1G	NVMFD5877NLWFT 3G	NVTJD4001NT1G	NZ9F2V7ST5G
NVF3055-100T1G	NVMFS5826NLT1G	NVTR01P02LT1G	NZ9F5V1T5G
NVF3055L108T1G	NVMFS5826NLT3G	NVTR0202PLT1G	NZ9F6V2ST5G
NVF3055L108T3G	NVMFS5832NLT1G	NVTR4502PT1G	NZH10C
NVF5P03T3G	NVMFS5832NLT3G	NVTR4503NT1G	NZH11C
NVF6P02T3G	NVMFS5834NLT1G	NX2301P	NZH12B
NVMD3P03R2G	NVMFS5834NLT3G	NX3008NBK	NZH13B
NVMFD5485NLT1G	NVMFS5834NLT3G	NX3008NBKMB	NZH15B

# Multisim 14.0 Education Components

---

NZH16C	NZQA6V8AXV5T1G	NZX20B	NZX5V1D
NZH18C	NZQA6V8AXV5T2G	NZX22A	NZX5V6A
NZH20C	NZQA6V8AXV5T3G	NZX22B	NZX5V6B
NZH22C	NZX10A	NZX24A	NZX5V6C
NZH24C	NZX10C	NZX24B	NZX5V6D
NZH27C	NZX11A	NZX27A	NZX5V6E
NZH30C	NZX11C	NZX27B	NZX6V2B
NZH3V0B	NZX11D	NZX27C	NZX6V2C
NZH3V3A	NZX12A	NZX2V4A	NZX6V2D
NZH3V6B	NZX12B	NZX2V7B	NZX6V2E
NZH3V9B	NZX12C	NZX30A	NZX6V8A
NZH4V3B	NZX12D	NZX30C	NZX6V8B
NZH4V7B	NZX13B	NZX33C	NZX6V8C
NZH5V1B	NZX13C	NZX36C	NZX7V5A
NZH5V6B	NZX14A	NZX3V0B	NZX7V5B
NZH6V2B	NZX14B	NZX3V3B	NZX7V5D
NZH6V8B	NZX14C	NZX3V3C	NZX8V2A
NZH7V5C	NZX15B	NZX3V6C	NZX8V2B
NZH8V2B	NZX16A	NZX3V9C	NZX8V2D
NZH9V1B	NZX16B	NZX4V3C	NZX9V1B
NZL5V6ATT1G	NZX16C	NZX4V7A	NZX9V1E
NZL5V6AXV3T1G	NZX18A	NZX4V7C	OCTAL_REG
NZL6V8AXV3T1G	NZX18B	NZX4V7D	OHN3019U
NZL7V5AXV3T1G	NZX18C	NZX5V1B	OHN3030U
NZQA5V6XV5T1G	NZX20A	NZX5V1C	OHN3040U

# Multisim 14.0 Education Components

---

OHN3075U	OP05CH	OP07CJG	OP10Y
OHN3113U	OP05CJ	OP07CN8	OP113EP
OHN3119U	OP05CJ8	OP07CP	OP113ES
OHN3175U	OP05CN8	OP07CS8	OP113FP
OHS3019U	OP05CP	OP07DD	OP113FS
OHS3030U	OP05CZ	OP07DJG	OP1177AR
OHS3040U	OP05EH	OP07DP	OP1177ARM
OHS3075U	OP05EJ	OP07ED	OP11GP
OHS3119U	OP05EJ8	OP07EH	OP11GS
OHS3175U	OP05EN8	OP07EJ8	OP12BJ
OL	OP05EP	OP07EJG	OP12BZ/883
OP01CZ	OP05EZ	OP07EN8	OP12EJ
OP01J	OP05H	OP07EP	OP12EZ
OP02AJ	OP05J	OP07H	OP15AH
OP02AZ	OP05J8	OP07J	OP15AJ
OP02CJ	OP06AJ	OP07J8	OP15AZ
OP02CP	OP06GJ	OP07RC/883	OP15BH
OP02CZ	OP06GZ	OP07Y	OP15BJ/883
OP04AK	OP07AH	OP07Z	OP15BZ/883
OP04AY	OP07AJ	OP08	OP15CH
OP04EY	OP07AJ8	OP09AY	OP15EH
OP05AH	OP07AZ	OP09BY	OP15EJ
OP05AJ	OP07CD	OP10AY	OP15EZ
OP05AJ8	OP07CH	OP10CY	OP15FH
OP05AZ	OP07CJ8	OP10EY	OP15FJ

# Multisim 14.0 Education Components

---

OP15FP	OP16EZ	OP184ES	OP20HS
OP15FZ	OP16FH	OP191GP	OP20HZ
OP15GH	OP16FJ	OP191GS	OP213AZ/883
OP15GJ	OP16FP	OP193EP	OP213BZ/883
OP15GN8	OP16FZ	OP193ES	OP213EP
OP15GP	OP16GH	OP193FP	OP213ES
OP15GS	OP16GJ	OP193FS	OP213EZ
OP15GZ	OP16GN8	OP196GP	OP213FP
OP160ARC/883	OP16GP	OP196GS	OP213FS
OP160AZ	OP16GS	OP200AZ	OP215AH
OP160FZ	OP16GZ	OP200EZ	OP215AJ
OP160GP	OP176GP	OP200FZ	OP215AJ8
OP160GS	OP176GS	OP200GP	OP215AZ
OP162DRU	OP177AZ	OP200GS	OP215BJ/883
OP162GS	OP177BRC/883	OP207AY	OP215BRC/883
OP162GSZ	OP177BZ	OP207EY	OP215BZ/883
OP16AH	OP177EZ	OP207FY	OP215CH
OP16AJ	OP177FP	OP20BJ	OP215CJ/883
OP16BH	OP177FS	OP20BZ	OP215CJ8
OP16BJ/883	OP177FZ	OP20CZ	OP215CZ/883
OP16BZ/883	OP177GP	OP20FP	OP215EH
OP16C	OP177GS	OP20GJ	OP215EJ
OP16CH	OP177GZ	OP20GP	OP215EJ8
OP16EH	OP183GP	OP20GZ	OP215EN8
OP16EJ	OP183GS	OP20HJ	OP215EP

# Multisim 14.0 Education Components

---

OP215EZ	OP220CJ	OP22HP	OP262HRUZ-REEL
OP215FJ	OP220CZ	OP22HS	OP270EZ
OP215FP	OP220EZ	OP22HZ	OP270FZ
OP215FZ	OP220FZ	OP237AJ	OP270GP
OP215GH	OP220GJ	OP237CJ	OP270GS
OP215GJ8	OP220GP	OP237EJ	OP275GP
OP215GN8	OP220GS	OP237EN	OP275GS
OP215GP	OP220GZ	OP237GJ	OP279GP
OP215GS	OP221AJ/883	OP237GN	OP279GS
OP215GZ	OP221AZ	OP249AJ	OP279HRU
OP2177AR	OP221BJ	OP249ARC/883	OP27AH
OP2177ARM	OP221CJ	OP249AZ	OP27AJ
OP2177ARMZ	OP221EZ	OP249EJ	OP27AJ8
OP2177ARZ	OP221GJ	OP249FJ	OP27AJG
OP21AJ	OP221GP	OP249FZ	OP27AL
OP21AZ	OP221GS	OP249GP	OP27AZ
OP21EZ	OP221GZ	OP249GS	OP27BJ
OP21FJ	OP227AJ	OP260AJ	OP27BR/883
OP21FP	OP227CJ	OP260ARC/883	OP27BZ
OP21FZ	OP227EJ	OP260GP	OP27CH
OP21GJ	OP227EN	OP260GS	OP27CJ
OP21GP	OP227GJ	OP262DRU	OP27CJ8
OP21HS	OP227GN	OP262DRUZ-REEL	OP27CJG
OP220AJ	OP22AJ/883	OP262GS	OP27CZ
OP220AZ	OP22AZ	OP262GSZ	OP27EH



# Multisim 14.0 Education Components

---

OP27EJ	OP283GS	OP296GP	OP37BJ
OP27EJ8	OP284EP	OP296GS	OP37BRC/883
OP27EN8	OP284ES	OP296HRU	OP37BZ
OP27EP	OP284FP	OP297ARC/883	OP37CH
OP27EPZ	OP284FS	OP297AZ	OP37CJ
OP27EZ	OP285GP	OP297AZ/883	OP37CJ8
OP27FJ	OP285GS	OP297EZ	OP37CJG
OP27FP	OP290ARC/883	OP297FP	OP37CZ
OP27FZ	OP290AZ	OP297FZ	OP37EH
OP27GH	OP290EZ	OP297GP	OP37EJ
OP27GJ	OP290FZ	OP297GS	OP37EJ8
OP27GJ8	OP290GP	OP32AZ	OP37EN8
OP27GJZ	OP290GS	OP32EP	OP37EP
OP27GN8	OP291GP	OP32EZ	OP37EZ
OP27GP	OP291GS	OP32FP	OP37FJ
OP27GPZ	OP292GP	OP32FZ	OP37FP
OP27GS	OP292GS	OP32GP	OP37FZ
OP27GSZ	OP293EP	OP32GZ	OP37GH
OP27GZ	OP293ES	OP37AFK	OP37GJ
OP281GRU	OP293FP	OP37AH	OP37GJ8
OP281GS	OP293FS	OP37AJ	OP37GN8
OP282AZ/883	OP295A	OP37AJ8	OP37GP
OP282GP	OP295AP	OP37AJG	OP37GS
OP282GS	OP295GP	OP37AL	OP37GZ
OP283GP	OP295GS	OP37AZ	OP400ATC/883

# Multisim 14.0 Education Components

---

OP400AY	OP420FY	OP43	OP481GS
OP400EY	OP420GP	OP43A	OP482ARC/883
OP400FY	OP420GS	OP43B	OP482AY/883
OP400GP	OP420GY	OP43E	OP482GP
OP400GS	OP420HP	OP43F	OP484EP
OP400HP	OP420HS	OP43G	OP484ES
OP400HS	OP420HY	OP44AJ	OP484FP
OP413EP	OP421BY	OP462DRU	OP484FPZ
OP413ES	OP421CY	OP462DRUZ-REEL	OP484FS
OP413EY	OP421FY	OP462DS	OP490ATC/883
OP413FP	OP421GP	OP462GS	OP490AY
OP413FS	OP421GS	OP462GSZ	OP490EY
OP4177AR	OP421GY	OP462HRU-REEL	OP490FY
OP4177ARU	OP421HP	OP462HRUZ-REEL	OP490GP
OP4177ARUZ	OP421HS	OP467ARC/883	OP490GS
OP4177ARZ	OP421HY	OP467AY/883	OP491GP
OP41AJ	OP42AJ	OP467GP	OP491GS
OP41BJ	OP42ARC/883	OP467GS	OP491GSZ
OP41EJ	OP42AZ	OP470ARC/883	OP492GP
OP41FJ	OP42EJ	OP470ATC/883	OP492GS
OP41GP	OP42EZ	OP470AY	OP493EP
OP41GS	OP42FJ	OP470EY	OP493ES
OP420BY	OP42FZ	OP470GP	OP493FP
OP420CRC/883	OP42GP	OP470GS	OP493FS
OP420CY	OP42GS	OP481GRU	OP495GP

# Multisim 14.0 Education Components

---

OP495GS	OP64ARC/883	OP90ARC/883	OPA124PB
OP495GSZ	OP64AZ	OP90AZ	OPA124U
OP496GP	OP64GP	OP90EZ	OPA124UA
OP496GS	OP64GS	OP90FZ	OPA124UB
OP496HRU	OP727AR	OP90GP	OPA128JM
OP497AY	OP727ARU	OP90GS	OPA128KM
OP497BRC/883	OP727ARUZ	OP950	OPA128LM
OP497BY	OP747AR	OP97AJ	OPA128SM
OP497CY	OP747ARU	OP97AZ	OPA129P
OP497FP	OP777AR	OP97EP	OPA129PB
OP497FS	OP777ARM	OP97FJ	OPA129U
OP497FY	OP77BJ	OP97FP	OPA129UB
OP497GP	OP77BRC/883	OP97FS	OPA130PA
OP497GS	OP77BZ	OP97FZ	OPA130UA
OP497GY	OP77EZ	OP999	OPA131PA
OP50AY	OP77FJ	OPA1013CN8	OPA131PJ
OP50BY	OP77FZ	OPA1013DN8	OPA131UA
OP50EY	OP77GP	OPA111AM	OPA131UJ
OP50FY	OP77GS	OPA111BM	OPA132P
OP61ARC/883	OP80BJ	OPA111SM	OPA132PA
OP61AZ	OP80EJ	OPA121KM	OPA132U
OP61FZ	OP80FJ	OPA121KP	OPA132UA
OP61GP	OP80GP	OPA121KU	OPA134PA
OP61GS	OP80GS	OPA124P	OPA134UA
OP64AJ	OP906	OPA124PA	OPA137N

# Multisim 14.0 Education Components

---

OPA137NA	OPA209AID	OPA2131PJ	OPA2227U
OPA137P	OPA209AIDBVR	OPA2131UA	OPA2227UA
OPA137PA	OPA209AIDGKR	OPA2131UJ	OPA2234P
OPA137U	OPA209AIDR	OPA2132P	OPA2234PA
OPA137UA	OPA2107AM	OPA2132PA	OPA2234U
OPA140AID	OPA2107AP	OPA2132U	OPA2234UA
OPA140AIDBVR	OPA2107AU	OPA2132UA	OPA2237EA
OPA140AIDGKR	OPA2107BM	OPA2134PA	OPA2237UA
OPA140AIDR	OPA2107SM	OPA2134UA	OPA2241PA
OPA141AIDGKR	OPA2111AM	OPA2137E	OPA2241UA
OPA141AIDR	OPA2111BM	OPA2137EA	OPA2244EA
OPA1612AID	OPA2111KM	OPA2137P	OPA2244PA
OPA1632D	OPA2111KP	OPA2137PA	OPA2244UA
OPA1632DGN	OPA2111SM	OPA2137U	OPA2251PA
OPA1642AID	OPA211AID	OPA2137UA	OPA2251UA
OPA1642AIDGKR	OPA211AIDGKR	OPA2140AID	OPA2277P
OPA1642AIDR	OPA211AIDR	OPA2140AIDGKR	OPA2277PA
OPA1644AID	OPA211AIDRGR	OPA2140AIDR	OPA2277U
OPA1644AIPW	OPA211ID	OPA2141AIDGKR	OPA2277UA
OPA177EZ	OPA211IDGKR	OPA2141AIDR	OPA227P
OPA177FP	OPA211IDR	OPA2209AID	OPA227PA
OPA177FZ	OPA211IDRGR	OPA2209AIDGKR	OPA227U
OPA177GP	OPA2130PA	OPA2209AIDR	OPA227UA
OPA177GS	OPA2130UA	OPA2227P	OPA228P
OPA177GZ	OPA2131PA	OPA2227PA	OPA228U

# Multisim 14.0 Education Components

---

OPA2300AIDGSR	OPA2340PA	OPA2357AIDGSR	OPA2381AIDGKR
OPA2301AID	OPA2340UA	OPA2363AIDGSR	OPA2381AIDRBT
OPA2301AIDGKR	OPA2342EA	OPA2363AIRSVR	OPA241PA
OPA2301AIDR	OPA2342UA	OPA2363IDGSR	OPA241UA
OPA2317ID	OPA2344EA/250	OPA2369AIDCNR	OPA244NA
OPA2317IDGKR	OPA2344PA	OPA2369AIDGKR	OPA244PA
OPA2330AID	OPA2344UA	OPA2373AIDGSR	OPA244UA
OPA2330AIDGKR	OPA2347EA	OPA2373AIDRCR	OPA251PA
OPA2330AIDR	OPA2347UA	OPA2374AID	OPA251UA
OPA2330AIDRBR	OPA2349EA/250	OPA2374AIDCNR	OPA2541AM
OPA2330AIDRG4	OPA2349UA	OPA2374AIDG4	OPA2541BM
OPA2333AIDGKR	OPA234E	OPA2376AID	OPA2541SM
OPA2333AIDR	OPA234EA	OPA2376AIDGKR	OPA2544T
OPA2333AIDRBR	OPA234P	OPA2376AIDR	OPA2604AP
OPA2333AIDRG4	OPA234PA	OPA2376AIYZDR	OPA2604AU
OPA2334AIDGSR	OPA234U	OPA2377AID	OPA2613ID
OPA2335AID	OPA234UA	OPA2377AIDGKR	OPA2613IDTJ
OPA2335AIDGKR	OPA2350EA	OPA2377AIDR	OPA2614ID
OPA2335AIDR	OPA2350PA	OPA2378AIDCNR	OPA2614IDTJ
OPA2337EA/250	OPA2350UA	OPA2379AID	OPA2652E
OPA2337PA	OPA2353EA/250	OPA2379AIDCNR	OPA2652U
OPA2337UA	OPA2353UA	OPA2379AIDG4	OPA2658P
OPA2338EA/250	OPA2354AIDDA	OPA237NA	OPA2658PB
OPA2338UA	OPA2354AIDGKR	OPA237UA	OPA2658U
OPA2340EA	OPA2355DGSA/250	OPA2380AIDGKR	OPA2658UB

# Multisim 14.0 Education Components

---

OPA2677T	OPA2725AID	OPA27FJ	OPA333AID
OPA2677U	OPA2725AIDGKR	OPA27FZ	OPA333AIDBVR
OPA2680N	OPA2725AIDR	OPA27GJ	OPA333AIDCKR
OPA2680U	OPA2726AIDGST	OPA27GP	OPA333AIDG4
OPA2681N	OPA2727AID	OPA27GU	OPA334AID
OPA2681U	OPA2727AIDRBR	OPA27GZ	OPA335EA/250
OPA2682N	OPA2727AIDRG4	OPA2822E/250	OPA335UA
OPA2682U	OPA2735AID	OPA2822U	OPA335AID
OPA2683ID	OPA2735AIDGKR	OPA2835ID	OPA335AIDBV
OPA2683IDCNR	OPA2735AIDR	OPA2835IDGS	OPA336N/250
OPA2683IDG4	OPA2743EA/250	OPA2835IRMCR	OPA336NA/250
OPA2683IDGST	OPA2743PA	OPA2835IRUNR	OPA336NJ/250
OPA2684ID	OPA2743UA	OPA2836ID	OPA336U
OPA2684IDCNR	OPA277P	OPA2836IDGS	OPA336UA
OPA2686U	OPA277PA	OPA2836IRUNR	OPA337EA/250
OPA2690I-14D	OPA277U	OPA2846ID	OPA337NA/250
OPA2690ID	OPA277UA	OPA300AID	OPA337PA
OPA2691I-14D	OPA27AJ	OPA300AIDBV	OPA337UA
OPA2691ID	OPA27AZ	OPA301AID	OPA338NA/250
OPA2703EA/250	OPA27BJ	OPA301AIDBV	OPA338UA
OPA2703PA	OPA27BZ	OPA317ID	OPA340NA
OPA2703UA	OPA27CJ	OPA317IDBVR	OPA340PA
OPA2704EA/250	OPA27CZ	OPA317IDCKR	OPA340UA
OPA2704PA	OPA27EJ	OPA320AIDBVR	OPA342NA
OPA2704UA	OPA27EZ	OPA320SAIDBVR	OPA342PA

# Multisim 14.0 Education Components

---

OPA342UA	OPA355NA	OPA374AID	OPA37GZ
OPA343NA	OPA355UA	OPA374AIDBV	OPA380AID
OPA343UA	OPA357AIDBV	OPA377AID	OPA380AIDGK
OPA344NA	OPA3583AM	OPA377AIDBVR	OPA381AIDGK
OPA344PA	OPA3583JM	OPA377AIDCKR	OPA404AG
OPA344UA	OPA358AIDCK	OPA377AIDR	OPA404BG
OPA345NA	OPA360AIDCK	OPA378AIDBVR	OPA404KP
OPA345UA	OPA363ID	OPA378AIDCKR	OPA404KU
OPA347NA	OPA363IDBV	OPA379AID	OPA404SG
OPA347PA	OPA364ID	OPA379AIDBVR	OPA4130PA
OPA347SA	OPA364IDBV	OPA379AIDCKR	OPA4130UA
OPA347UA	OPA365AID	OPA379AIDG4	OPA4131NA
OPA348AID	OPA365AIDBVR	OPA37AJ	OPA4131NJ
OPA348AIDBV	OPA3680E	OPA37AZ	OPA4131PA
OPA348AIDCKR	OPA3680U	OPA37BJ	OPA4131PJ
OPA349NA	OPA3681E	OPA37BZ	OPA4131UA
OPA349SA	OPA3681U	OPA37CJ	OPA4132PA
OPA349UA	OPA3682E	OPA37CZ	OPA4132UA
OPA350EA	OPA3682U	OPA37EJ	OPA4134UA
OPA350PA	OPA3690ID	OPA37EZ	OPA4137P
OPA350UA	OPA3690IDBQR	OPA37FJ	OPA4137PA
OPA353NA	OPA3690IDG4	OPA37FZ	OPA4137U
OPA353UA	OPA369AIDCKR	OPA37GJ	OPA4137UA
OPA354AIDBV	OPA373AID	OPA37GP	OPA4140AID
OPA354AIDDA	OPA373AIDBV	OPA37GU	OPA4140AIPW

# Multisim 14.0 Education Components

---

OPA4141AID	OPA4340PA	OPA4658U	OPA541SM
OPA4141AIPW	OPA4340UA	OPA4658UB	OPA544F
OPA4209AIPW	OPA4342EA	OPA4684ID	OPA544T
OPA4227PA	OPA4342PA	OPA4684IPWT	OPA547T
OPA4227UA	OPA4342UA	OPA4703EA/250	OPA548T
OPA4228PA	OPA4347EA	OPA4703UA	OPA549S
OPA4228UA	OPA4347UA	OPA4704EA/250	OPA549T
OPA4234PA	OPA4348AID	OPA4704UA	OPA551FA/500
OPA4234U	OPA4348AIP	OPA4743EA/250	OPA551FAKTWT
OPA4234UA	OPA4354AID	OPA4743UA	OPA551PA
OPA4237UA	OPA4354AIPWR	OPA4820ID	OPA551UA
OPA4241PA	OPA4374AID	OPA4820IPWR	OPA552FA/500
OPA4241UA	OPA4374AIPWR	OPA4872ID	OPA552FAKTWT
OPA4243EA	OPA4377AIPW	OPA501AM	OPA552PA
OPA4244EA	OPA4379AIPWR	OPA501BM	OPA552UA
OPA4251PA	OPA445AP	OPA501RM	OPA561PWP
OPA4251UA	OPA445BM	OPA501SM	OPA564AIDWD
OPA4277PA	OPA445SM	OPA502BM	OPA564AIDWP
OPA4277UA	OPA452TA	OPA502SM	OPA567AIRHGR
OPA4317ID	OPA454AIDDA	OPA511AM	OPA569AIDWP
OPA4317IPW	OPA4650P	OPA512BM	OPA600BM
OPA4330AID	OPA4650PB	OPA512SM	OPA600CM
OPA4330AIPW	OPA4650U	OPA541AM	OPA600SM
OPA4330AIRGYR	OPA4658P	OPA541AP	OPA600TM
OPA4340EA	OPA4658PB	OPA541BM	OPA602AM



# Multisim 14.0 Education Components

---

OPA602AP	OPA623AP	OPA641PB	OPA648U
OPA602AU	OPA623AU	OPA641U	OPA650N
OPA602BM	OPA627AM	OPA641UB	OPA650NB
OPA602BP	OPA627AP	OPA642H	OPA650P
OPA602CM	OPA627AU	OPA642HSQ	OPA650PB
OPA602SM	OPA627BM	OPA642P	OPA650U
OPA603AP	OPA627BP	OPA642PB	OPA650UB
OPA603AU	OPA627SM	OPA642U	OPA651N
OPA604AP	OPA628AP	OPA642UB	OPA651NB
OPA604AU	OPA628AU	OPA643H	OPA651P
OPA606KM	OPA633KP	OPA643HSQ	OPA651PB
OPA606KP	OPA637AM	OPA643P	OPA651U
OPA606LM	OPA637AP	OPA643PB	OPA651UB
OPA620KG	OPA637AU	OPA643U	OPA653IDBVR
OPA620KP	OPA637BM	OPA643UB	OPA653IDRBR
OPA620KU	OPA637BP	OPA644U	OPA654AM
OPA620LG	OPA637SM	OPA644UB	OPA655H
OPA620SG	OPA640H	OPA646H	OPA655HSQ
OPA621KG	OPA640HSQ	OPA646HSQ	OPA655P
OPA621KP	OPA640P	OPA646P	OPA655PB
OPA621KU	OPA640U	OPA646PB	OPA655UB
OPA621LG	OPA640UB	OPA646U	OPA656N
OPA621SG	OPA641H	OPA646UB	OPA656U
OPA622AP	OPA641HSQ	OPA648H	OPA658N
OPA622AU	OPA641P	OPA648P	OPA658P

# Multisim 14.0 Education Components

---

OPA658U	OPA684ID	OPA728AIDRBT	OPAMP_3T_VIRTU AL
OPA659IDBVR	OPA684IDBV	OPA734AID	OPAMP_5T_VIRTU AL
OPA659IDRBR	OPA686N	OPA734AIDBV	Op-Amp_741
OPA671AP	OPA686U	OPA735AID	OPAMP_RATED
OPA675JG	OPA687N	OPA735AIDBV	OPS665rx
OPA675KG	OPA687U	OPA743NA	OPS665tx
OPA675SG	OPA690ID	OPA743PA	OPS666rx
OPA676JG	OPA690IDBV	OPA743UA	OPS666tx
OPA676KG	OPA694ID	OPA77EZ	OPS667rx
OPA676SG	OPA694IDBVR	OPA77FP	OPS667tx
OPA678AG	OPA698ID	OPA77FZ	OPS690rx
OPA678AP	OPA699ID	OPA77GP	OPS690tx
OPA678AU	OPA703NA	OPA820ID	OPS691rx
OPA678SG	OPA703PA	OPA820IDBVR	OPS691tx
OPA680N	OPA703UA	OPA820IDG4	OPS692rx
OPA680P	OPA704NA	OPA827AID	OPS692tx
OPA680U	OPA704PA	OPA827AIDGKR	OPS693rx
OPA681N	OPA704UA	OPA835IDBVR	OPS693tx
OPA681P	OPA725AID	OPA836IDBVR	OPS695rx
OPA681U	OPA725AIDBV	OPA842ID	OPS695tx
OPA682N	OPA726AID	OPA842IDBV	OPS696rx
OPA682P	OPA726AIDGK	OPA847ID	OPS696tx
OPA682U	OPA727AIDGKR	OPA847IDBV	OPS697rx
OPA683BV	OPA727AIDRBT	OPA860ID	OPS697tx
OPA683ID	OPA728AIDGKT		

# Multisim 14.0 Education Components

---

OPS698rx	OUTPUT_MODULE_ 120Vdc	P6KE200ARLG	PA02A
OPS698tx		P6KE6.8AG	PA03
OPT301M	OUTPUT_MODULE_ 120Vrms	P6KE6.8ARLG	PA03A
OPTOCOUPLER_VIRTUAL	OUTPUT_MODULE_ 12Vdc	P6KE8.2A-E3/54	PA04
		P6KE9.1A-E3/54	PA04A
OR2	OUTPUT_MODULE_ 12Vrms	P6SMB11CAT3G	PA05
OR2		P6SMB13AT3G	PA05A
OR3	OUTPUT_MODULE_ 240Vdc	P6SMB15AT3G	PA07
OR3	OUTPUT_MODULE_ 240Vrms	P6SMB18AT3G	PA07A
OR4		P6SMB20AT3G	PA07M/883
OR4	OUTPUT_MODULE_ 24Vdc	P6SMB22AT3G	PA08
OR5		P6SMB22CAT3G	PA08/883
OR5	OUTPUT_MODULE_ 24Vrms	P6SMB24A-E3/52	PA08A
OR6	OUTPUT_MODULE_ 5Vdc	P6SMB24AT3G	PA09
OR6		P6SMB24CA-E3/52	PA09A
OR7	OUTPUT_MODULE_ 75Vdc	P6SMB24CAT3G	PA10
OR7	OVERLOAD	P6SMB33A-E3/52	PA10A
OR8	P121	P6SMB33AT3G	PA10M/883
OR8	P123	P6SMB36A-E3/52	PA12
OSM910P	P4KE10CA-E3/54	P6SMB43CAT3G	PA12A
OSTV7163151	P4KE300A/3	P6SMB6.8AT3G	PA12M/883
OSTV7203101	P4SMA36CA-E3/61	P6SMB62AT3G	PA21
OSTV7203151	P6KE100A-E3/54	P6SMB68AT3G	PA21A
OUTPUT_COIL	P6KE10A-E3/54	PA01	PA25
OUTPUT_COIL_NEGATED	P6KE200AG	PA02	PA25A

# Multisim 14.0 Education Components

---

PA41	PB_DPST	PBLS1501V	PBLS4003D
PA41A	PB_NC	PBLS1501Y	PBLS4003V
PA41M/883	PB_NO	PBLS1502V	PBLS4003Y
PA45	PB50	PBLS1502Y	PBLS4004D
PA51	PB58	PBLS1503V	PBLS4004V
PA51A	PB58A	PBLS1503Y	PBLS4004Y
PA51M/883	PBHV8115T	PBLS1504V	PBLS4005D
PA81J	PBHV8115X	PBLS1504Y	PBLS4005V
PA83	PBHV8115Z	PBLS2001D	PBLS4005Y
PA83A	PBHV8118T	PBLS2001S	PBLS6001D
PA83M/883	PBHV8140Z	PBLS2002D	PBLS6002D
PA84	PBHV8215Z	PBLS2002S	PBLS6003D
PA84A	PBHV8540T	PBLS2003D	PBLS6004D
PA84M/883	PBHV8540X	PBLS2003S	PBLS6005D
PA85	PBHV8540Z	PBLS2004D	PBLS6021D
PA85A	PBHV9040T	PBLS2021D	PBLS6022D
PA85M	PBHV9040X	PBLS2022D	PBLS6023D
PA87	PBHV9040Z	PBLS2023D	PBLS6024D
PA87A	PBHV9050T	PBLS2024D	PBRN113ET
PA88	PBHV9050Z	PBLS4001D	PBRN113ZT
PA88A	PBHV9115T	PBLS4001V	PBRN123ET
PA89	PBHV9115X	PBLS4001Y	PBRN123YT
PA89A	PBHV9115Z	PBLS4002D	PBRP113ET
PAR_GEN_CHK	PBHV9215Z	PBLS4002V	PBRP113ZT
PB_DPST	PBHV9540Z	PBLS4002Y	PBRP123ET

# Multisim 14.0 Education Components

---

PBRP123YT	PBSS303PD	PBSS3540MB	PBSS4041PX
PBSS2515E	PBSS303PX	PBSS4021NT	PBSS4041PZ
PBSS2515M	PBSS303PZ	PBSS4021NX	PBSS4041SN
PBSS2515MB	PBSS304ND	PBSS4021NZ	PBSS4041SP
PBSS2515VPN	PBSS304NX	PBSS4021PT	PBSS4041SPN
PBSS2515VS	PBSS304NZ	PBSS4021PX	PBSS4112PAN
PBSS2515YPN	PBSS304PD	PBSS4021PZ	PBSS4112PANP
PBSS2540E	PBSS304PX	PBSS4021SN	PBSS4120T
PBSS2540M	PBSS304PZ	PBSS4021SP	PBSS4130PAN
PBSS2540MB	PBSS305ND	PBSS4021SPN	PBSS4130PANP
PBSS301ND	PBSS305NX	PBSS4032ND	PBSS4130QA
PBSS301NX	PBSS305NZ	PBSS4032NT	PBSS4130T
PBSS301NZ	PBSS305PD	PBSS4032NX	PBSS4140DPN
PBSS301PD	PBSS305PX	PBSS4032NZ	PBSS4140T
PBSS301PX	PBSS305PZ	PBSS4032PD	PBSS4140U
PBSS301PZ	PBSS306NX	PBSS4032PT	PBSS4140V
PBSS302ND	PBSS306NZ	PBSS4032PX	PBSS4160DPN
PBSS302NX	PBSS306PX	PBSS4032PZ	PBSS4160DS
PBSS302NZ	PBSS306PZ	PBSS4032SN	PBSS4160PAN
PBSS302PD	PBSS3515E	PBSS4032SP	PBSS4160PANP
PBSS302PX	PBSS3515M	PBSS4032SPN	PBSS4160QA
PBSS302PZ	PBSS3515MB	PBSS4041NT	PBSS4160T
PBSS303ND	PBSS3515VS	PBSS4041NX	PBSS4160U
PBSS303NX	PBSS3540E	PBSS4041NZ	PBSS4160V
PBSS303NZ	PBSS3540M	PBSS4041PT	PBSS4220V

# Multisim 14.0 Education Components

---

PBSS4230PAN	PBSS4440D	PBSS5220V	PBSS5480X
PBSS4230PANP	PBSS4480X	PBSS5230PAP	PBSS5520X
PBSS4230QA	PBSS4520X	PBSS5230QA	PBSS5540X
PBSS4230T	PBSS4540X	PBSS5230T	PBSS5540Z
PBSS4240DPN	PBSS4540Z	PBSS5240T	PBSS5560PA
PBSS4240T	PBSS4560PA	PBSS5240V	PBSS5580PA
PBSS4240V	PBSS4580PA	PBSS5240X	PBSS5612PA
PBSS4240X	PBSS4612PA	PBSS5240Y	PBSS5620PA
PBSS4240Y	PBSS4620PA	PBSS5250T	PBSS5630PA
PBSS4250X	PBSS4630PA	PBSS5250X	PBSS8110D
PBSS4260PAN	PBSS5112PAP	PBSS5260PAP	PBSS8110T
PBSS4260PANP	PBSS5120T	PBSS5260QA	PBSS8110X
PBSS4260QA	PBSS5130PAP	PBSS5320D	PBSS8110Y
PBSS4320T	PBSS5130QA	PBSS5320T	PBSS8110Z
PBSS4320X	PBSS5130T	PBSS5320X	PBSS8510PA
PBSS4330PA	PBSS5140T	PBSS5330PA	PBSS9110D
PBSS4330X	PBSS5140U	PBSS5330X	PBSS9110T
PBSS4350D	PBSS5140V	PBSS5350D	PBSS9110X
PBSS4350SPN	PBSS5160DS	PBSS5350SS	PBSS9110Y
PBSS4350SS	PBSS5160PAP	PBSS5350T	PBSS9110Z
PBSS4350T	PBSS5160QA	PBSS5350X	PBSS9410PA
PBSS4350X	PBSS5160T	PBSS5350Z	PCP1208-TD-H
PBSS4350Z	PBSS5160U	PBSS5360Z	PD15-22B/TR8
PBSS4360Z	PBSS5160V	PBSS5420D	PD15-22C/TR8
PBSS4420D	PBSS5220T	PBSS5440D	PD70-01B/TR7

# Multisim 14.0 Education Components

---

PD93-21C/TR8	PDTA114TMB	PDTA123JMB	PDTA124XT
PD95-21B/TR10	PDTA114TT	PDTA123JT	PDTA124XU
PDB-C134	PDTA114TU	PDTA123JU	PDTA143EE
PDB-C134F	PDTA114YE	PDTA123TM	PDTA143EM
PDB-C139	PDTA114YM	PDTA123TMB	PDTA143EMB
PDB-C142D	PDTA114YMB	PDTA123TT	PDTA143ET
PDB-C152SM	PDTA114YT	PDTA123TU	PDTA143EU
PDB-C156	PDTA114YU	PDTA123YE	PDTA143TE
PDTA113EE	PDTA115EE	PDTA123YM	PDTA143TM
PDTA113EM	PDTA115EM	PDTA123YMB	PDTA143TMB
PDTA113EMB	PDTA115EMB	PDTA123YT	PDTA143TT
PDTA113ET	PDTA115ET	PDTA123YU	PDTA143TU
PDTA113EU	PDTA115EU	PDTA124EE	PDTA143XE
PDTA113ZE	PDTA115TE	PDTA124EM	PDTA143XM
PDTA113ZM	PDTA115TM	PDTA124EMB	PDTA143XMB
PDTA113ZMB	PDTA115TMB	PDTA124ET	PDTA143XT
PDTA113ZT	PDTA115TT	PDTA124EU	PDTA143XU
PDTA113ZU	PDTA115TU	PDTA124TE	PDTA143ZE
PDTA114EE	PDTA123EE	PDTA124TM	PDTA143ZM
PDTA114EM	PDTA123EM	PDTA124TMB	PDTA143ZMB
PDTA114EMB	PDTA123EMB	PDTA124TT	PDTA143ZT
PDTA114ET	PDTA123ET	PDTA124TU	PDTA143ZU
PDTA114EU	PDTA123EU	PDTA124XE	PDTA144EE
PDTA114TE	PDTA123JE	PDTA124XM	PDTA144EM
PDTA114TM	PDTA123JM	PDTA124XMB	PDTA144EMB

# Multisim 14.0 Education Components

---

PDTA144ET	PDTC114ET	PDTC123ET	PDTC124TT
PDTA144EU	PDTC114EU	PDTC123EU	PDTC124TU
PDTA144TE	PDTC114TE	PDTC123JE	PDTC124XE
PDTA144TM	PDTC114TM	PDTC123JM	PDTC124XM
PDTA144TMB	PDTC114TMB	PDTC123JMB	PDTC124XMB
PDTA144TT	PDTC114TT	PDTC123JT	PDTC124XT
PDTA144TU	PDTC114TU	PDTC123JU	PDTC124XU
PDTA144VE	PDTC114YE	PDTC123TE	PDTC143EE
PDTA144VM	PDTC114YM	PDTC123TM	PDTC143EM
PDTA144VMB	PDTC114YMB	PDTC123TMB	PDTC143EMB
PDTA144VT	PDTC114YT	PDTC123TT	PDTC143ET
PDTA144VU	PDTC114YU	PDTC123TU	PDTC143EU
PDTA144WE	PDTC115EE	PDTC123YE	PDTC143TE
PDTA144WM	PDTC115EM	PDTC123YM	PDTC143TM
PDTA144WMB	PDTC115EMB	PDTC123YMB	PDTC143TMB
PDTA144WT	PDTC115ET	PDTC123YT	PDTC143TT
PDTA144WU	PDTC115EU	PDTC123YU	PDTC143TU
PDTB113ET	PDTC115TE	PDTC124EE	PDTC143XE
PDTB113ZT	PDTC115TM	PDTC124EM	PDTC143XM
PDTB123ET	PDTC115TMB	PDTC124EMB	PDTC143XMB
PDTB123TT	PDTC115TT	PDTC124ET	PDTC143XT
PDTB123YT	PDTC115TU	PDTC124EU	PDTC143XU
PDTC114EE	PDTC123EE	PDTC124TE	PDTC143ZE
PDTC114EM	PDTC123EM	PDTC124TM	PDTC143ZM
PDTC114EMB	PDTC123EMB	PDTC124TMB	PDTC143ZMB



# Multisim 14.0 Education Components

---

PDTC143ZT	PDTD123TT	PEMB1	PEMD19
PDTC143ZU	PDTD123YT	PEMB10	PEMD2
PDTC144EE	PDZ10B	PEMB11	PEMD20
PDTC144EM	PDZ11B	PEMB13	PEMD24
PDTC144EMB	PDZ12B	PEMB14	PEMD3
PDTC144ET	PDZ13B	PEMB15	PEMD30
PDTC144EU	PDZ15B	PEMB16	PEMD4
PDTC144TE	PDZ16B	PEMB17	PEMD48
PDTC144TM	PDZ18B	PEMB18	PEMD6
PDTC144TMB	PDZ2.7B	PEMB19	PEMD9
PDTC144TT	PDZ20B	PEMB2	PEMF21
PDTC144TU	PDZ22B	PEMB20	PEMH1
PDTC144VE	PDZ24B	PEMB24	PEMH10
PDTC144VM	PDZ3.0B	PEMB3	PEMH11
PDTC144VMB	PDZ3.3B	PEMB30	PEMH13
PDTC144VT	PDZ3.6B	PEMB4	PEMH14
PDTC144VU	PDZ3.9B	PEMB9	PEMH15
PDTC144WE	PDZ4.3B	PEMD10	PEMH16
PDTC144WM	PDZ4.7B	PEMD12	PEMH17
PDTC144WMB	PDZ5.1B	PEMD13	PEMH18
PDTC144WT	PDZ5.6B	PEMD14	PEMH19
PDTC144WU	PDZ6.2B	PEMD15	PEMH2
PDTD113ET	PDZ6.8B	PEMD16	PEMH20
PDTD113ZT	PDZ7.5B	PEMD17	PEMH24
PDTD123ET	PDZ9.1B	PEMD18	PEMH30

# Multisim 14.0 Education Components

---

PEMH4	PESD15VS1ULD	PESD36VS2UT	PESD3V3V4UK
PEMH7	PESD15VS2UAT	PESD3V3L1BA	PESD3V3V4UW
PEMH9	PESD15VS2UQ	PESD3V3L1UA	PESD5V0F1BL
PEMT1	PESD15VS2UT	PESD3V3L1UB	PESD5V0F1BLD
PEMX1	PESD15VS4UD	PESD3V3L1UL	PESD5V0F5UF
PEMZ1	PESD15VS5UD	PESD3V3L2BT	PESD5V0F5UV
PEMZ7	PESD15VU1UT	PESD3V3L2UM	PESD5V0L1BA
PESD12VL1BA	PESD16VX1UL	PESD3V3L4UF	PESD5V0L1UA
PESD12VL2BT	PESD1CAN	PESD3V3L4UG	PESD5V0L1UB
PESD12VS1UA	PESD1FLEX	PESD3V3L4UW	PESD5V0L1UL
PESD12VS1UB	PESD1LIN	PESD3V3L5UF	PESD5V0L1ULD
PESD12VS1UJ	PESD24VL1BA	PESD3V3L5UK	PESD5V0L2BT
PESD12VS1UL	PESD24VL2BT	PESD3V3L5UV	PESD5V0L2UM
PESD12VS1ULD	PESD24VS1UA	PESD3V3L5UY	PESD5V0L4UF
PESD12VS2UAT	PESD24VS1UB	PESD3V3S1UB	PESD5V0L4UG
PESD12VS2UQ	PESD24VS1UL	PESD3V3S1UL	PESD5V0L4UW
PESD12VS2UT	PESD24VS1ULD	PESD3V3S2UAT	PESD5V0L5UK
PESD12VS4UD	PESD24VS2UAT	PESD3V3S2UQ	PESD5V0L5UV
PESD12VS5UD	PESD24VS2UQ	PESD3V3S2UT	PESD5V0L5UY
PESD12VU1UT	PESD24VS2UT	PESD3V3S4UD	PESD5V0L6UAS
PESD12VV1BL	PESD24VS4UD	PESD3V3S4UF	PESD5V0L6US
PESD15VL1BA	PESD24VS5UD	PESD3V3S5UD	PESD5V0L7BAS
PESD15VL2BT	PESD24VU1UT	PESD3V3U1UT	PESD5V0L7BS
PESD15VS1UB	PESD2CAN	PESD3V3V4UF	PESD5V0S1BA
PESD15VS1UL	PESD36VS1UL	PESD3V3V4UG	PESD5V0S1BB

# Multisim 14.0 Education Components

---

PESD5V0S1BL	PESD5V0V1BLD	PHILIPS-MIPS-HDR	PID_CONTROLLER
PESD5V0S1BLD	PESD5V0V4UF	PHN110	PIECEWISE_LINEAR_CURRENT
PESD5V0S1UA	PESD5V0V4UG	PhonePlug	PIECEWISE_LINEAR_VOLTAGE
PESD5V0S1UB	PESD5V0V4UK	PhonePlug2	
PESD5V0S1UJ	PESD5V0V4UW	PHOTO_DIODE_RATED	PIMC31
PESD5V0S1UL	PESD5V0X1BCAL	PHOTO_TRANSISTOR_RATED	PIMN31
PESD5V0S1ULD	PESD5V0X1BCL		PIMT1
PESD5V0S2BT	PESD5V0X1BL	PHOTODIODE	PIMZ2
PESD5V0S2UAT	PESD5V0X1BQ	PHOTOTRANSISTOR	PJ-002B-SMT
PESD5V0S2UQ	PESD5V0X1BT	PHP125	PJ-007
PESD5V0S4UD	PESD5V0X1UAB	PHP225	PJ1-023
PESD5V0S4UF	PESD5V0X1UALD	PHPT60603NY	PJ-102A
PESD5V0S5UD	PESD5V0X1UB	PHPT60603PY	PLD-JTAG-HDR
PESD5V0U1BA	PESD5V0X1ULD	PHPT61002NYC	PLL_VIRTUAL
PESD5V0U1BB	PESD5V2S2UT	PHPT61002PYC	PLUS_MINUS_ONE
PESD5V0U1BL	PESD9V0V4UK	PHPT61003NY	PLUS_MINUS_ONE_BLUE
PESD5V0U1BLD	PESD9X5.0L	PHPT61003PY	PLUS_MINUS_ONE_GREEN
PESD5V0U1UA	PESD9X7.0L	PHT4NQ10LT	PLUS_MINUS_ONE_ORANGE
PESD5V0U1UB	PG_13	PHT6N06LT	PLUS_MINUS_ONE_YELLOW
PESD5V0U1UL	PG_9_O_E	PHT6N06T	
PESD5V0U1UT	PHASE_ANGLE_CONTROLLER	PHT6NQ10T	
PESD5V0U2BT	PHASE_ANGLE_CONTROLLER_2PULSE	PHT8N06LT	
PESD5V0V1BA	PHASE_ANGLE_CONTROLLER_6PULSE	PI_CONTROLLER	PLVA2656A
PESD5V0V1BB		PIC16F84	PLVA650A
PESD5V0V1BL		PIC16F84A	PLVA662A

# Multisim 14.0 Education Components

---

PMBD353	PMBFJ177	PMBT3946YPN	PMBZ5234B
PMBD354	PMBFJ210	PMBT4401	PMBZ5235B
PMBD6050	PMBFJ211	PMBT4403	PMBZ5236B
PMBD6100	PMBFJ212	PMBT5550	PMBZ5237B
PMBD7000	PMBFJ308	PMBT5551	PMBZ5238B
PMBD7100	PMBFJ309	PMBT6428	PMBZ5239B
PMBD914	PMBFJ310	PMBT6429	PMBZ5240B
PMBF170	PMBS3904	PMBTA06	PMBZ5241B
PMBF4391	PMBS3906	PMBTA13	PMBZ5242B
PMBF4392	PMBT2222	PMBTA14	PMBZ5243B
PMBF4393	PMBT2222A	PMBTA42	PMBZ5244B
PMBF4416	PMBT2369	PMBTA42DS	PMBZ5245B
PMBF4416A	PMBT2907	PMBTA44	PMBZ5246B
PMBF5484	PMBT2907A	PMBTA45	PMBZ5247B
PMBF5485	PMBT3904	PMBTA56	PMBZ5248B
PMBF5486	PMBT3904M	PMBTA64	PMBZ5249B
PMBFJ108	PMBT3904MB	PMBTA92	PMBZ5250B
PMBFJ109	PMBT3904VS	PMBZ5226B	PMBZ5251B
PMBFJ110	PMBT3904YS	PMBZ5227B	PMBZ5252B
PMBFJ111	PMBT3906	PMBZ5228B	PMBZ5253B
PMBFJ112	PMBT3906M	PMBZ5229B	PMBZ5254B
PMBFJ113	PMBT3906MB	PMBZ5230B	PMBZ5255B
PMBFJ174	PMBT3906VS	PMBZ5231B	PMBZ5256B
PMBFJ175	PMBT3906YS	PMBZ5232B	PMBZ5257B
PMBFJ176	PMBT3946VPN	PMBZ5233B	PMDPB28UN

# Multisim 14.0 Education Components

---

PMDPB30XN	PMEG2005CT	PMEG2015EA	PMEG3005ELD
PMDPB38UNE	PMEG2005EB	PMEG2015EH	PMEG3005ESF
PMDPB42UN	PMEG2005EH	PMEG2015EJ	PMEG3005ET
PMDPB55XP	PMEG2005EJ	PMEG2015EPK	PMEG3010BEA
PMDPB56XN	PMEG2005EL	PMEG2015EV	PMEG3010BEP
PMDPB58UPE	PMEG2005ELD	PMEG2020AEA	PMEG3010BER
PMDPB70EN	PMEG2005EPK	PMEG2020CPA	PMEG3010BEV
PMDPB70XP	PMEG2005ESF	PMEG2020EH	PMEG3010CEH
PMDPB70XPE	PMEG2005ET	PMEG2020EJ	PMEG3010CEJ
PMDPB85UPE	PMEG2010AEB	PMEG2020EPA	PMEG3010EB
PMDPB95XNE	PMEG2010AEH	PMEG2020EPK	PMEG3010EH
PMDT290UNE	PMEG2010AEJ	PMEG3002AEB	PMEG3010EJ
PMDT670UPE	PMEG2010AET	PMEG3002AEL	PMEG3010EP
PMEG1020EA	PMEG2010BEA	PMEG3002AELD	PMEG3010ER
PMEG1020EH	PMEG2010BELD	PMEG3002AESF	PMEG3010ET
PMEG1020EJ	PMEG2010BER	PMEG3002EJ	PMEG3015EH
PMEG1020EV	PMEG2010BEV	PMEG3002TV	PMEG3015EJ
PMEG1030EH	PMEG2010EA	PMEG3005AEA	PMEG3015EV
PMEG1030EJ	PMEG2010EH	PMEG3005AESF	PMEG3020BEP
PMEG2005AEA	PMEG2010EJ	PMEG3005AEV	PMEG3020BER
PMEG2005AEL	PMEG2010EPA	PMEG3005CT	PMEG3020CEP
PMEG2005AELD	PMEG2010EPK	PMEG3005EB	PMEG3020CPA
PMEG2005AESF	PMEG2010ER	PMEG3005EH	PMEG3020DEP
PMEG2005AEV	PMEG2010ET	PMEG3005EJ	PMEG3020EH
PMEG2005BELD	PMEG2010EV	PMEG3005EL	PMEG3020EJ

# Multisim 14.0 Education Components

---

PMEG3020EP	PMEG4010EH	PMEG6010AED	PMF87EN
PMEG3020EPA	PMEG4010EJ	PMEG6010CEH	PMG45UN
PMEG3020ER	PMEG4010EP	PMEG6010CEJ	PMG85XP
PMEG3030BEP	PMEG4010EPK	PMEG6010CPA	PMGD130UN
PMEG3030EP	PMEG4010ER	PMEG6010ELR	PMGD175XN
PMEG3050BEP	PMEG4010ET	PMEG6010EP	PMGD280UN
PMEG3050EP	PMEG4010ETP	PMEG6010ER	PMGD290XN
PMEG4002AESF	PMEG4010ETR	PMEG6010ETR	PMGD370XN
PMEG4002EB	PMEG4015EPK	PMEG6020ELR	PMGD400UN
PMEG4002EJ	PMEG4020EP	PMEG6020EP	PMGD780SN
PMEG4002EL	PMEG4020EPA	PMEG6020EPA	PMGD8000LN
PMEG4002ELD	PMEG4020EPK	PMEG6020ER	PML260SN
PMEG4002ESF	PMEG4020ER	PMEG6020ETP	PML340SN
PMEG4005AEA	PMEG4020ETP	PMEG6020ETR	PMLL4148L
PMEG4005AEV	PMEG4020ETR	PMEG6030EP	PMLL4448
PMEG4005CT	PMEG4030EP	PMEG6030ETP	PMLL5225B
PMEG4005EH	PMEG4030ER	PMF170XP	PMLL5226B
PMEG4005EJ	PMEG4030ETP	PMF250XN	PMLL5227B
PMEG4005EPK	PMEG4050EP	PMF280UN	PMLL5228B
PMEG4005ET	PMEG4050ETP	PMF290XN	PMLL5229B
PMEG4010BEA	PMEG45A10EPD	PMF3800SN	PMLL5230B
PMEG4010BEV	PMEG45U10EPD	PMF400UN	PMLL5231B
PMEG4010CEH	PMEG6002EB	PMF63UN	PMLL5232B
PMEG4010CEJ	PMEG6002EJ	PMF77XN	PMLL5233B
PMEG4010CPA	PMEG6002TV	PMF780SN	PMLL5234B

# Multisim 14.0 Education Components

---

PMLL5235B	PMLL5260B	PMN80XP	PMPB27EP
PMLL5236B	PMLL5261B	PMP4201G	PMPB29XNE
PMLL5237B	PMLL5262B	PMP4201V	PMPB29XPE
PMLL5238B	PMLL5263B	PMP4201Y	PMPB33XN
PMLL5239B	PMLL5264B	PMP4501G	PMPB33XP
PMLL5240B	PMLL5265B	PMP4501V	PMPB43XPE
PMLL5241B	PMLL5266B	PMP4501Y	PMPB47XP
PMLL5242B	PMMT491A	PMP5201G	PMR280UN
PMLL5243B	PMMT591A	PMP5201V	PMR290UNE
PMLL5244B	PMN20EN	PMP5201Y	PMR290XN
PMLL5245B	PMN22XN	PMP5501G	PMR370XN
PMLL5246B	PMN25EN	PMP5501V	PMR400UN
PMLL5247B	PMN25UN	PMP5501Y	PMR670UPE
PMLL5248B	PMN27UP	PMPB10XNE	PMR780SN
PMLL5249B	PMN27XPE	PMPB11EN	PMSS3904
PMLL5250B	PMN28UN	PMPB12UN	PMSS3906
PMLL5251B	PMN34UN	PMPB13XNE	PMST2222
PMLL5252B	PMN34UP	PMPB15XN	PMST2222A
PMLL5253B	PMN35EN	PMPB15XP	PMST2369
PMLL5254B	PMN40LN	PMPB16XN	PMST2907A
PMLL5255B	PMN40UPE	PMPB19XP	PMST3904
PMLL5256B	PMN42XPE	PMPB20EN	PMST3906
PMLL5257B	PMN48XP	PMPB20UN	PMST4401
PMLL5258B	PMN50UPE	PMPB20XPE	PMST4403
PMLL5259B	PMN70XPE	PMPB23XNE	PMST5088

# Multisim 14.0 Education Components

---

PMST5089	PMV30XN	PMZB670UPE	PN4143
PMST5550	PMV31XN	PMZB790SN	PN4248
PMST5551	PMV32UP	PN2222	PN4249
PMST6428	PMV33UPE	PN2222A	PN4250
PMST6429	PMV37EN	PN2369	PN4250A
PMSTA05	PMV40UN	PN2369A	PN4258
PMSTA06	PMV45EN	PN2484	PN4258A
PMSTA42	PMV48XP	PN2906	PN4274
PMSTA55	PMV50UPE	PN2906A	PN4275
PMSTA56	PMV60EN	PN2907	PN4354
PMSTA92	PMV65UN	PN2907A	PN4355
PMT200EN	PMV65XP	PN3565	PN4356
PMT21EN	PMV90EN	PN3638	PN4391
PMT29EN	PMZ1000UN	PN3638A	PN4392
PMT760EN	PMZ250UN	PN3640	PN4393
PMV117EN	PMZ270XN	PN3641	PN4416
PMV160UP	PMZ350XN	PN3642	PN4416A
PMV16UN	PMZ390UN	PN3643	PN4916
PMV170UN	PMZ760SN	PN3644	PN4917
PMV185XN	PMZB290UN	PN3645	PN5128
PMV20XN	PMZB300XN	PN3646	PN5129
PMV213SN	PMZB350UPE	PN3694	PN5133
PMV22EN	PMZB370UNE	PN4121	PN5134
PMV28UN	PMZB380XN	PN4122	PN5135
PMV30UN	PMZB420UN	PN4141	PN5136



# Multisim 14.0 Education Components

---

PN5137	PROBE_DIG_YELLOW	PSMN016-100XS	PSMN1R1-25YLC
PN5138	PROBE_GREEN	PSMN017-60YS	PSMN1R1-30PL
PN5139	PROBE_ORANGE	PSMN017-80PS	PSMN1R1-40BS
PN5142	PROBE_RED	PSMN018-80YS	PSMN1R2-25YL
PN5179	PROBE_YELLOW	PSMN020-100YS	PSMN1R2-25YLC
PN5910	PRTR5V0U1T	PSMN020-30MLC	PSMN1R2-30YLC
PN930	PRTR5V0U2X	PSMN022-30PL	PSMN1R3-30YL
PNS40010ER	PSMN011-60ML	PSMN025-100D	PSMN1R5-25YL
POLYNOMIAL_VOLTAGE	PSMN011-60MS	PSMN026-80YS	PSMN1R5-30BLE
POTENTIOMETER	PSMN011-80YS	PSMN027-100PS	PSMN1R5-30YL
POTENTIOMETER_RATED	PSMN012-100YS	PSMN027-100XS	PSMN1R5-30YLC
POTENTIOMETER_VIRTUAL	PSMN012-60YS	PSMN028-100YS	PSMN1R5-40ES
Potentiometer1_5K	PSMN012-80PS	PSMN030-60YS	PSMN1R5-40PS
POWERVCO	PSMN013-100BS	PSMN034-100PS	PSMN1R6-30PL
POWERVCO2	PSMN013-100ES	PSMN038-100YL	PSMN1R6-40YLC
PROBE	PSMN013-100PS	PSMN039-100YS	PSMN1R7-30YL
PROBE_BLUE	PSMN013-100XS	PSMN040-100MSE	PSMN1R7-60BS
PROBE_DIG	PSMN013-100YSE	PSMN041-80YL	PSMN1R8-30PL
PROBE_DIG_BLUE	PSMN013-30MLC	PSMN045-80YS	PSMN1R8-40YLC
PROBE_DIG_GREEN	PSMN013-30YLC	PSMN057-200B	PSMN1R9-40PL
PROBE_DIG_ORANGE	PSMN013-80YS	PSMN059-150Y	PSMN2R0-30PL
PROBE_DIG_ORANGE	PSMN014-40YS	PSMN069-100YS	PSMN2R0-30YL
PROBE_DIG_RED	PSMN015-60PS	PSMN075-100MSE	PSMN2R0-30YLE
	PSMN016-100PS	PSMN0R9-25YLC	PSMN2R0-60ES
		PSMN1R0-30YLC	PSMN2R0-60PS

# Multisim 14.0 Education Components

---

PSMN2R1-40PL	PSMN3R4-30PL	PSMN5R0-100ES	PSMN7R6-100BSE
PSMN2R2-25YLC	PSMN3R5-30YL	PSMN5R0-100PS	PSMN7R6-60PS
PSMN2R2-30YLC	PSMN3R5-80ES	PSMN5R0-100XS	PSMN7R8-120ES
PSMN2R2-40PS	PSMN3R5-80PS	PSMN5R0-30YL	PSMN7R8-120PS
PSMN2R5-30YL	PSMN3R8-100BS	PSMN5R0-80PS	PSMN8R0-40PS
PSMN2R5-60PL	PSMN3R9-25MLC	PSMN5R5-60YS	PSMN8R2-80YS
PSMN2R6-30YLC	PSMN3R9-60PS	PSMN5R6-100PS	PSMN8R3-40YS
PSMN2R6-40YS	PSMN3R9-60XS	PSMN5R6-100XS	PSMN8R5-100ES
PSMN2R6-60PS	PSMN4R0-25YLC	PSMN5R8-40YS	PSMN8R5-100PS
PSMN2R7-30PL	PSMN4R0-30YL	PSMN6R0-25YLB	PSMN8R5-100XS
PSMN2R8-25MLC	PSMN4R0-30YLD	PSMN6R0-30YL	PSMN8R5-60YS
PSMN2R8-40PS	PSMN4R0-40YS	PSMN6R0-30YLB	PSMN8R7-80PS
PSMN2R8-80BS	PSMN4R1-30YLC	PSMN6R0-30YLD	PSMN9R0-25MLC
PSMN2R9-25YLC	PSMN4R2-60PL	PSMN6R1-30YLD	PSMN9R5-100PS
PSMN2R9-30MLC	PSMN4R3-100ES	PSMN6R3-120ES	PSMN9R5-100XS
PSMN3R0-30MLC	PSMN4R3-100PS	PSMN6R3-120PS	PSMN9R5-30YLC
PSMN3R0-30YL	PSMN4R3-30PL	PSMN6R5-25YLC	PSMN9R8-30MLC
PSMN3R0-60ES	PSMN4R3-80ES	PSMN6R5-80PS	PSMNR90-30BL
PSMN3R0-60PS	PSMN4R3-80PS	PSMN7R0-100ES	PTVS10VP1UP
PSMN3R3-40YS	PSMN4R4-30MLC	PSMN7R0-100PS	PTVS10VP1UTP
PSMN3R3-60PL	PSMN4R4-80PS	PSMN7R0-100XS	PTVS10VS1UR
PSMN3R3-80BS	PSMN4R5-40PS	PSMN7R0-30MLC	PTVS10VS1UTR
PSMN3R3-80ES	PSMN4R6-100XS	PSMN7R0-30YL	PTVS11VP1UP
PSMN3R3-80PS	PSMN4R6-60PS	PSMN7R0-30YLC	PTVS11VP1UTP
PSMN3R4-30BLE	PSMN4R8-100BSE	PSMN7R0-60YS	PTVS11VS1UR

# Multisim 14.0 Education Components

---

PTVS11VS1UTR	PTVS18VP1UP	PTVS30VP1UTP	PTVS45VS1UR
PTVS12VP1UP	PTVS18VP1UTP	PTVS30VS1UR	PTVS45VS1UTR
PTVS12VP1UTP	PTVS18VS1UR	PTVS30VS1UTR	PTVS48VP1UP
PTVS12VS1UR	PTVS18VS1UTR	PTVS33VP1UP	PTVS48VP1UTP
PTVS12VS1UTR	PTVS20VP1UP	PTVS33VP1UTP	PTVS48VS1UR
PTVS13VP1UP	PTVS20VP1UTP	PTVS33VS1UR	PTVS48VS1UTR
PTVS13VP1UTP	PTVS20VS1UR	PTVS33VS1UTR	PTVS51VP1UP
PTVS13VS1UR	PTVS20VS1UTR	PTVS36VP1UP	PTVS51VP1UTP
PTVS13VS1UTR	PTVS22VP1UP	PTVS36VP1UTP	PTVS51VS1UR
PTVS14VP1UP	PTVS22VP1UTP	PTVS36VS1UR	PTVS51VS1UTR
PTVS14VP1UTP	PTVS22VS1UR	PTVS36VS1UTR	PTVS54VP1UP
PTVS14VS1UR	PTVS22VS1UTR	PTVS3V3P1UP	PTVS54VP1UTP
PTVS14VS1UTR	PTVS24VP1UP	PTVS3V3P1UTP	PTVS54VS1UR
PTVS15VP1UP	PTVS24VP1UTP	PTVS3V3S1UR	PTVS54VS1UTR
PTVS15VP1UTP	PTVS24VS1UR	PTVS3V3S1UTR	PTVS58VP1UP
PTVS15VS1UR	PTVS24VS1UTR	PTVS40VP1UP	PTVS58VP1UTP
PTVS15VS1UTR	PTVS26VP1UP	PTVS40VP1UTP	PTVS58VS1UR
PTVS16VP1UP	PTVS26VP1UTP	PTVS40VS1UR	PTVS58VS1UTR
PTVS16VP1UTP	PTVS26VS1UR	PTVS40VS1UTR	PTVS5V0P1UP
PTVS16VS1UR	PTVS26VS1UTR	PTVS43VP1UP	PTVS5V0P1UTP
PTVS16VS1UTR	PTVS28VP1UP	PTVS43VP1UTP	PTVS5V0S1UR
PTVS17VP1UP	PTVS28VP1UTP	PTVS43VS1UR	PTVS5V0S1UTR
PTVS17VP1UTP	PTVS28VS1UR	PTVS43VS1UTR	PTVS60VP1UP
PTVS17VS1UR	PTVS28VS1UTR	PTVS45VP1UP	PTVS60VP1UTP
PTVS17VS1UTR	PTVS30VP1UP	PTVS45VP1UTP	PTVS60VS1UR

# Multisim 14.0 Education Components

---

PTVS60VS1UTR	PTVS8V5S1UR	PUMD18	PUSH_BUTTON_DP ST
PTVS64VP1UP	PTVS8V5S1UTR	PUMD19	PUSH_CM
PTVS64VP1UTP	PTVS9V0P1UP	PUMD2	PUSH_VM
PTVS6V0P1UP	PTVS9V0P1UTP	PUMD20	PWM
PTVS6V0P1UTP	PTVS9V0S1UR	PUMD24	PWM_3PHASE
PTVS6V0S1UR	PTVS9V0S1UTR	PUMD3	PWM_COMPLEME NTARY
PTVS6V0S1UTR	PULLUP_RATED	PUMD30	PWM_SINUSOIDAL _3PHASE
PTVS6V5P1UP	PULSE_CURRENT	PUMD48	PWMCM
PTVS6V5P1UTP	PULSE_VOLTAGE	PUMD6	PWMCM2
PTVS6V5S1UR	PUMB1	PUMD9	PWMCMX
PTVS6V5S1UTR	PUMB11	PUMH1	PWMVM
PTVS7V0P1UP	PUMB13	PUMH10	PWMVM2
PTVS7V0P1UTP	PUMB14	PUMH11	PXT2222A
PTVS7V0S1UR	PUMB19	PUMH13	PXT2907A
PTVS7V0S1UTR	PUMB2	PUMH2	PXT4401
PTVS7V5P1UP	PUMB24	PUMH30	PXT4403
PTVS7V5P1UTP	PUMB3	PUMH4	PXTA14
PTVS7V5S1UR	PUMB30	PUMH7	PXTA42
PTVS7V5S1UTR	PUMB4	PUMH9	PXTA92
PTVS8V0P1UP	PUMB9	PUMT1	PZFJ108
PTVS8V0P1UTP	PUMD10	PUMX1	PZFJ109
PTVS8V0S1UR	PUMD12	PUMX2	PZFJ110
PTVS8V0S1UTR	PUMD13	PUMZ1	PZT2222
PTVS8V5P1UP	PUMD14	PUMZ2	
PTVS8V5P1UTP	PUMD15		

# Multisim 14.0 Education Components

---

PZT2222A	PZU10B2	PZU12B3	PZU15B2L
PZT2222AT1G	PZU10B2A	PZU12B3A	PZU15B3
PZT2907	PZU10B2L	PZU12BA	PZU15B3A
PZT2907A	PZU10B3	PZU12BL	PZU15BA
PZT2907AT1	PZU10B3A	PZU12DB2	PZU15BL
PZT2907AT1G	PZU10BA	PZU13B	PZU15DB2
PZT2907AT3G	PZU10BL	PZU13B1	PZU16B
PZT3904	PZU10DB2	PZU13B1A	PZU16B1
PZT3906	PZU11B	PZU13B2	PZU16B1A
PZT43	PZU11B1	PZU13B2A	PZU16B2
PZT4401	PZU11B1A	PZU13B2L	PZU16B2A
PZT4403	PZU11B2	PZU13B3	PZU16B2L
PZT651T1	PZU11B2A	PZU13B3A	PZU16B3
PZT651T1G	PZU11B2L	PZU13BA	PZU16B3A
PZT751T1	PZU11B3	PZU13BL	PZU16BA
PZT751T1G	PZU11B3A	PZU13DB2	PZU16BL
PZTA14	PZU11BA	PZU14B2	PZU16DB2
PZTA42	PZU11BL	PZU14B2A	PZU18B
PZTA44	PZU11DB2	PZU14B2L	PZU18B1
PZTA92	PZU12B	PZU14DB2	PZU18B1A
PZTA92T1G	PZU12B1	PZU15B	PZU18B2
PZTA93	PZU12B1A	PZU15B1	PZU18B2A
PZU10B	PZU12B2	PZU15B1A	PZU18B2L
PZU10B1	PZU12B2A	PZU15B2	PZU18B3
PZU10B1A	PZU12B2L	PZU15B2A	PZU18B3A

# Multisim 14.0 Education Components

---

PZU18BA	PZU20DB2	PZU27BL	PZU3.6BA
PZU18BL	PZU22B	PZU3.0B	PZU3.6BL
PZU18DB2	PZU22B1	PZU3.0B1	PZU3.6DB2
PZU2.4B	PZU22B1A	PZU3.0B1A	PZU3.9B
PZU2.4BA	PZU22B2	PZU3.0B2	PZU3.9B1
PZU2.4BL	PZU22B2A	PZU3.0B2A	PZU3.9B1A
PZU2.7B	PZU22B2L	PZU3.0B2L	PZU3.9B2
PZU2.7B1	PZU22B3	PZU3.0BA	PZU3.9B2A
PZU2.7B1A	PZU22B3A	PZU3.0BL	PZU3.9B2L
PZU2.7B2	PZU22BA	PZU3.0DB2	PZU3.9BA
PZU2.7B2A	PZU22BL	PZU3.3B	PZU3.9BL
PZU2.7B2L	PZU22DB2	PZU3.3B1	PZU3.9DB2
PZU2.7BA	PZU24B	PZU3.3B1A	PZU30B
PZU2.7BL	PZU24B1	PZU3.3B2	PZU30BA
PZU2.7DB2	PZU24B1A	PZU3.3B2A	PZU30BL
PZU20B	PZU24B2	PZU3.3B2L	PZU33B
PZU20B1	PZU24B2A	PZU3.3BA	PZU33BA
PZU20B1A	PZU24B2L	PZU3.3BL	PZU33BL
PZU20B2	PZU24B3	PZU3.3DB2	PZU36B
PZU20B2A	PZU24B3A	PZU3.6B	PZU36BA
PZU20B2L	PZU24BA	PZU3.6B1	PZU36BL
PZU20B3	PZU24BL	PZU3.6B1A	PZU4.3B
PZU20B3A	PZU24DB2	PZU3.6B2	PZU4.3B1
PZU20BA	PZU27B	PZU3.6B2A	PZU4.3B1A
PZU20BL	PZU27BA	PZU3.6B2L	PZU4.3B2

# Multisim 14.0 Education Components

---

PZU4.3B2A	PZU5.1B3A	PZU6.2DB2	PZU8.2B1A
PZU4.3B2L	PZU5.1BA	PZU6.8B	PZU8.2B2
PZU4.3B3	PZU5.1BL	PZU6.8B1	PZU8.2B2A
PZU4.3B3A	PZU5.1DB2	PZU6.8B1A	PZU8.2B2L
PZU4.3BA	PZU5.6B	PZU6.8B2	PZU8.2B3
PZU4.3BL	PZU5.6B1	PZU6.8B2A	PZU8.2B3A
PZU4.3DB2	PZU5.6B1A	PZU6.8B2L	PZU8.2BA
PZU4.7B	PZU5.6B2	PZU6.8B3	PZU8.2BL
PZU4.7B1	PZU5.6B2A	PZU6.8B3A	PZU8.2DB2
PZU4.7B1A	PZU5.6B2L	PZU6.8BA	PZU9.1B
PZU4.7B2	PZU5.6B3	PZU6.8BL	PZU9.1B1
PZU4.7B2A	PZU5.6B3A	PZU6.8DB2	PZU9.1B1A
PZU4.7B2L	PZU5.6BA	PZU7.5B	PZU9.1B2
PZU4.7B3	PZU5.6BL	PZU7.5B1	PZU9.1B2A
PZU4.7B3A	PZU5.6DB2	PZU7.5B1A	PZU9.1B2L
PZU4.7BA	PZU6.2B	PZU7.5B2	PZU9.1B3
PZU4.7BL	PZU6.2B1	PZU7.5B2A	PZU9.1B3A
PZU4.7DB2	PZU6.2B1A	PZU7.5B2L	PZU9.1BA
PZU5.1B	PZU6.2B2	PZU7.5B3	PZU9.1BL
PZU5.1B1	PZU6.2B2A	PZU7.5B3A	PZU9.1DB2
PZU5.1B1A	PZU6.2B2L	PZU7.5BA	Quad_And_Gate
PZU5.1B2	PZU6.2B3	PZU7.5BL	QUAD_MUX_2TO1
PZU5.1B2A	PZU6.2B3A	PZU7.5DB2	QUAD_REG
PZU5.1B2L	PZU6.2BA	PZU8.2B	R145-32.768kHz
PZU5.1B3	PZU6.2BL	PZU8.2B1	R26-32.768kHz

# Multisim 14.0 Education Components

---

R38-32.768kHz	RC4558Y	REF01AJ/883C	REF192FS
R710XPT	RC4559D	REF01CJ	REF192GP
R711XPT	RC4559P	REF01CP	REF192GPZ
R712XPT	RCJ-011-SMT	REF01CPZ	REF192GRU
R714XPT	RCJ-32234	REF01CS	REF192GRUZ
RAD_PER_SEC_TO_ RPM	RD10	REF01EZ	REF192GS
	RD11	REF01HPZ	REF193GS
RAD_TO_DEG	RD12	REF01HS	REF193GSZ
RB520CS3002L	RD15	REF01HZ	REF194ES
RB520CS30L	RD15SB	REF02AJ	REF194GP
RB520S30	RD2.0S	REF02AJ/883C	REF194GSZ
RB521CS30L	RD2.2S	REF02AZ	REF195ES
RB521S30	RD2.4S	REF02CP	REF195FS
RB521S30T1G	RD2.7S	REF02CS	REF195GP
RB521S30T5G	RD3.0S	REF02CZ	REF195GPZ
RB751CS40	RD4.7	REF02EZ	REF195GRU
RB751S40	RD5.1	REF02HPZ	REF195GRUZ
RB751S40T1G	RD5.6	REF02HSZ	REF195GS
RB751V40	RD6.2	REF02HZ	REF196GRU
RC_CHAIN_CAUER	RD6.8	REF02RC	REF196GRU-REEL7
RC_CHAIN_FOSTER	RD7.5	REF02RC/883C	REF196GS
RC4136D	RD7.5SB	REF191ES	REF196GSZ
RC4136N	RD8.2	REF191GP	REF198ES
RC4558D	RD9.2	REF191GS	REF198FSZ
RC4558P	REF01AJ	REF192ES	REF198GP



# Multisim 14.0 Education Components

---

REF198GRU	REF43GS	REF5045AIDGKR	RELAY1B_VIRTUAL
REF198GRUZ	REF5010AID	REF5045AIDR	RELAY1C_VIRTUAL
REF198GS	REF5010AIDGKR	REF5045ID	RESET_COIL
REF3120AIDBZR	REF5010ID	REF5045IDGKR	RESISTOR_RATED
REF3212AIDBVR	REF5010IDGKR	REF5045IDR	RESISTOR_VIRTUAL
REF3220AIDBVR	REF5020AID	REF5050AID	Resistor1_1.0k
REF3225AIDBVR	REF5020AIDGKR	REF5050AIDGKR	Resistor2_4.7k
REF3230AIDBVR	REF5020ID	REF5050AIDR	Resistor3_680
REF3233AIDBVR	REF5020IDGKR	REF5050ID	RESOLVER
REF3240AIDBVR	REF5025AID	REF5050IDGKR	REVERSE_1A
REF3312AIDBZR	REF5025AIDGKR	REF5050IDR	REVERSE_2A
REF3312AIDCKR	REF5025ID	REFVAR	REVERSE_3A
REF3318AIDBZR	REF5025IDGKR	REG_FILE_2Px4	REVERSE_4A
REF3318AIDCKR	REF5030AID	REG_FILE_4x4	RGF1A
REF3320AIDBZR	REF5030AIDGKR	RELAY_COIL	RGF1B
REF3320AIDCKR	REF5030ID	RELAY_COIL_NEGA TED	RGF1D
REF3325AIDBZR	REF5030IDGKR	RELAY_COIL_PULSE	RGF1G
REF3325AIDCKR	REF5030IDR	RELAY_CONTACT_N C	RGF1J
REF3330AIDBZR	REF5040AID	RELAY_CONTACT_N O	RGF1K
REF3330AIDCKR	REF5040AIDGKR	RELAY_NC	RGF1M
REF3333AIDBZR	REF5040AIDR	RELAY_NO	RGL34A
REF3333AIDCKR	REF5040ID	RELAY_NONC	RGL34B
REF43FZ	REF5040IDGKR	RELAY1A_VIRTUAL	RGL34D
REF43GP	REF5040IDR		RGL34G
REF43GPZ	REF5045AID		RGL34J

# Multisim 14.0 Education Components

---

RGP02-12E	RGP20J	RIBBON_14H_LATC H	RIBBON_24V_LATC H
RGP02-14E	RGP25A		
RGP02-16E	RGP25B	RIBBON_14H_MNT	RIBBON_24V_MNT
RGP02-18E	RGP25D	RIBBON_14V	RIBBON_26H
RGP02-20E	RGP25G	RIBBON_14V_LATC H	RIBBON_26H_LATC H
RGP02-20E-E3/54	RGP25J	RIBBON_14V_MNT	RIBBON_26H_MNT
RGP10A	RGP25K	RIBBON_16H	RIBBON_26V
RGP10B	RGP25M	RIBBON_16H_LATC H	RIBBON_26V_LATC H
RGP10D	RGP30A		
RGP10G	RGP30B	RIBBON_16H_MNT	RIBBON_26V_MNT
RGP10J	RGP30D	RIBBON_16V	RIBBON_30H
RGP10K	RGP30G	RIBBON_16V_LATC H	RIBBON_30H_LATC H
RGP10M	RGP30J	RIBBON_16V_MNT	RIBBON_30H_MNT
RGP10M-E3/54	RGP30K	RIBBON_20H	RIBBON_30V
RGP15A	RGP30M	RIBBON_20H_LATC H	RIBBON_30V_LATC H
RGP15B	R-HI-008068-2		
RGP15D	RIBBON_10H	RIBBON_20H_MNT	RIBBON_30V_MNT
RGP15G	RIBBON_10H_LATC H	RIBBON_20V	RIBBON_34H
RGP15J	RIBBON_10H_MNT	RIBBON_20V_LATC H	RIBBON_34H_LATC H
RGP15K			
RGP15M	RIBBON_10V	RIBBON_20V_MNT	RIBBON_34H_MNT
RGP20A	RIBBON_10V_LATC H	RIBBON_24H	RIBBON_34V
RGP20B	RIBBON_10V_MNT	RIBBON_24H_LATC H	RIBBON_34V_LATC H
RGP20D	RIBBON_14H	RIBBON_24H_MNT	RIBBON_34V_MNT
RGP20G		RIBBON_24V	RIBBON_40H

# Multisim 14.0 Education Components

---

RIBBON_40H_LATC H	RTD RV4136D	S3D-E3/57T S3M-E3/57T	SAF-C167CR-LM HA+
RIBBON_40H_MNT	RV4136N	S4PD-M3/86A	SAF-XC164TM- 4F40F AA
RIBBON_40V	RV4558D	S5227B	SAF-XC164TM- 4F40F AA
RIBBON_40V_LATC H	RV4558P	S5227G	
RIBBON_40V_MNT	S1227-1010BQ	S5227J	SAF-XC866-1FRA AB
RIBBON_50H	S1227-1010BR	S5227N	SAF-XC866-1FRA AB
RIBBON_50H_LATC H	S1227-16BQ	SA15AG	SAF-XC866L-1FRA AB
RIBBON_50H_MNT	S1227-16BR	SA15ARLG	SAF-XC866L-1FRA AB
RIBBON_50V	S1227-33BQ	SA2M-E3/5AT	
RIBBON_50V_LATC H	S1227-33BR	SA5.0A-E3/54	SAF-XC886-6FFA 5V AC
RIBBON_50V_MNT	S1227-66BQ	SA5.0CA-E3/54	SAF-XC886-6FFA 5V AC
	S1227-66BR	SA6.0A-E3/54	
RM4136FK	S1B-E3/61T	SA6.0CA-E3/54	SAF-XC886CLM- 6FFA 5V AC
RM4136J	S1D-E3/61T	SA9.0CA-E3/54	
RM4136W	S1G-E3/61T	SAB-C167CR-LM HA+	SAF-XC886CLM- 6FFA 5V AC
RM4558JG	S1J-E3/61T		
RMB4S-E3/45	S1PG-E3/84A	SAB-C167CR-LM HA+	SAF-XC886CM-6FFA 5V AC
RPM_TO_RAD_PER _SEC	S2800A	SAB-C167SR-LM HA+	SAF-XC886CM-6FFA 5V AC
	S2800B		
RS1G-E3/5AT	S2800D	SAB-C167SR-LM HA+	SAF-XC886LM-6FFA 5V AC
RS1K-E3/61T	S2800M		
RS2D-E3/52T	S2G-E3/52T	SAC5.0-E3/54	SAF-XC886LM-6FFA 5V AC
RS2J-E3/52T	S2SA1774G	SAF-C167CR-LM HA+	SAF-XC888-6FFA 5V AC
RS3D-E3/57T	S2SC4617G		

# Multisim 14.0 Education Components

---

SAF-XC888-6FFA 5V AC	SAK-XC2267-56F66L AC	SAK-XC2287-56F66L AC	SAK-XC2786X-96F66L AC
SAF-XC888CLM-6FFA 5V AC	SAK-XC2267-56F66L AC	SAK-XC2287-56F80L AC	SAK-XC2786X-96F66L AC
SAF-XC888CLM-6FFA 5V AC	SAK-XC2267-56F80L AC	SAK-XC2287-56F80L AC	SAK-XC866-1FRA AB SAK-XC866-1FRA AB
SAF-XC888CM-6FFA 5V AC	SAK-XC2267-56F80L AC	SAK-XC2287-96F66L AC	SAK-XC866L-1FRA AB
SAF-XC888CM-6FFA 5V AC	SAK-XC2285M-104F80L AA	SAK-XC2287-96F66L AC	SAK-XC866L-1FRA AB
SAF-XC888LM-6FFA 5V AC	SAK-XC2285M-104F80L AA	SAK-XC2287-96F80L AC	SAK-XC886-6FFA 5V AC
SAF-XC888LM-6FFA 5V AC	SAK-XC2285M-56F80L AA	SAK-XC2287-96F80L AC	SAK-XC886-6FFA 5V AC
SAK-C167CR-LM HA+	SAK-XC2285M-56F80L AA	SAK-XC2287M-104F80L AA	SAK-XC886CLM-6FFA 5V AC
SAK-C167CR-LM HA+	SAK-XC2285M-72F80L AA	SAK-XC2287M-104F80L AA	SAK-XC886CLM-6FFA 5V AC
SAK-C167SR-LM HA+	SAK-XC2285M-72F80L AA	SAK-XC2287M-56F80L AA	SAK-XC886CM-6FFA 5V AC
SAK-C167SR-LM HA+	SAK-XC2286-56F66L AC	SAK-XC2287M-56F80L AA	SAK-XC886CM-6FFA 5V AC
SAK-XC2264-56F66L AC	SAK-XC2286-56F66L AC	SAK-XC2287M-72F80L AA	SAK-XC886LM-6FFA 5V AC
SAK-XC2264-56F66L AC	SAK-XC2286-56F80L AC	SAK-XC2287M-72F80L AA	SAK-XC886LM-6FFA 5V AC
SAK-XC2264-56F80L AC	SAK-XC2286-56F80L AC	SAK-XC2766X-96F66L AC	SAK-XC888-6FFA 5V AC
SAK-XC2264-56F80L AC	SAK-XC2287-56F66L AC	SAK-XC2766X-96F66L AC	SAK-XC888-6FFA 5V AC

# Multisim 14.0 Education Components

---

SAK-XC888CLM-6FFA 5V AC	SB160-E3/54	SBAW56TT1G	SBCP56T1G
	SB2H100-E3/54	SBC807-16LT1G	SBCP56T3G
SAK-XC888CLM-6FFA 5V AC	SB2H90-E3/23	SBC807-16LT3G	SBCP68T1G
SAK-XC888CM-6FFA 5V AC	SB320	SBC807-25LT1G	SBE001-TL-E
	SB330	SBC807-25LT3G	SBE002-TL-E
SAK-XC888CM-6FFA 5V AC	SB340	SBC807-40LT1G	SBR640CTT4G
	SB350	SBC807-40LT3G	SBR660CTT4G
SAK-XC888LM-6FFA 5V AC	SB360	SBC817-25LT1G	SBR80520LT1G
	SB3H100-E3/54	SBC817-25LT3G	SBR80520LT3G
	SB520	SBC846ALT1G	SBR835LT4G
SAMPLE_BEND	SB530	SBC846BDW1T1G	SBRA8160T3G
SAMPLE_GENERIC	SB540	SBC846BLT1G	SBRB1045G
SAMPLE_LOSSY	SB540-E3/54	SBC846BLT3G	SBRB1045T4G
SAMPLE_MICROSTRIP	SB550	SBC846BPDW1T1G	SBRB1545CTG
	SB560	SBC846BPDW1T2G	SBRB1545CTT4G
SAMPLE_OPENEND	SB560-E3/54	SBC847BDW1T1G	SBRB20200CTT4G
SAMPLE_RFCAP	SBAS16DXV6T1G	SBC847BDW1T3G	SBRB2545CTG
SAMPLE_RFCOIL	SBAS20LT1G	SBC856ALT1G	SBRB2545CTT4G
SAMPLE_WAVEGUIDE	SBAT54CLT1G	SBC856BDW1T1G	SBRD81035CTLT4G
SB	SBAV70LT1G	SBC856BDW1T3G	SBRD81045T4G
SB01-15C-TB-E	SBAV70LT3G	SBC856BWT1G	SBRD8320G
SB040-E3/54	SBAV99LT1G	SBC857BDW1T1G	SBRD8320T4G
SB05-03Q-TL-E	SBAV99LT3G	SBCP56-10T1G	SBRD8330G
SB1003M3-TL-E	SBAW56LT1G	SBCP56-16T1G	SBRD8330T4G
SB140A-E3/54	SBAW56LT3G	SBCP56-16T3G	SBRD8340G

# Multisim 14.0 Education Components

---

SBRD8340T4G	SDTA114YET1G	SEVEN_SEG_COM_A_ORANGE	SEVEN_SEG_DECIMAL_COM_K_ORANGE
SBRD8350G	SDTC114EET1G		
SBRD8350T4G	SDTC114YET1G	SEVEN_SEG_COM_A_YELLOW	SEVEN_SEG_DECIMAL_COM_K_YELLOW
SBRD8360G	SDTC124EET1G	SEVEN_SEG_COM_K	
SBRD8360RLG	SE10PJ-M3/84A		SEVEN_SEG_TWO-DIGIT_COM_A
SBRD8360T4G	SE5534AFK	SEVEN_SEG_COM_K_BLUE	
SBRD8835LG	SE5534AJG		SEVEN_SEG_TWO-DIGIT_COM_A_BLUE
SBRD8835LT4G	SE5534FK	SEVEN_SEG_COM_K_GREEN	
SBR81100T3G	SE5534JG	SEVEN_SEG_COM_K_ORANGE	SEVEN_SEG_TWO-DIGIT_COM_A_GREEN
SBR8120T3G	SEAM-40-03.0-S-06-2-A-K-TR	SEVEN_SEG_COM_K_YELLOW	EN
SBR8130LT3G			SEVEN_SEG_TWO-DIGIT_COM_A_ORANGE
SBR8140T3G	SEAM-40-07.0-S-06-2-A-K-TR	SEVEN_SEG_DECIMAL_COM_A	NGE
SBR8190T3G	SEMICONDUCTOR_VIRTUAL	SEVEN_SEG_DECIMAL_COM_A_BLUE	SEVEN_SEG_TWO-DIGIT_COM_A_YELLOW
SBR8320T3G			OW
SBR8340T3G	SEMICONDUCTOR_VIRTUAL	SEVEN_SEG_DECIMAL_COM_A_GREEN	SEVEN_SEG_TWO-DIGIT_COM_K
SBS811-TL-E	RESISTOR_VIRTUAL		
SCH2202-TL-E	SEPICCM	SEVEN_SEG_DECIMAL_COM_A_ORANGE	SEVEN_SEG_TWO-DIGIT_COM_K_BLUE
SCHMITT_TRIGGER	SEPICVM	GE	E
SCR	SET_COIL	SEVEN_SEG_DECIMAL_COM_A_YELLOW	SEVEN_SEG_TWO-DIGIT_COM_K_GREEN
SCY99074DR2G	SEVEN_SEG_COM_A	W	EN
SD05T1G			
SD12CT1G	SEVEN_SEG_COM_A_BLUE	SEVEN_SEG_DECIMAL_COM_K	SEVEN_SEG_TWO-DIGIT_COM_K_ORANGE
SD12T1G			NGE
SD241	SEVEN_SEG_COM_A_GREEN	SEVEN_SEG_DECIMAL_COM_K_BLUE	
SD41		SEVEN_SEG_DECIMAL_COM_K_GREEN	SEVEN_SEG_TWO-DIGIT_COM_K_YELLOW
			OW

# Multisim 14.0 Education Components

---

SFH 203 FA	SFH615A-3X017	SFH6719	Si1016CX-T1-GE3
SFH 205 F	SFH617A-3	SFH6720T	Si1050X-T1-GE3
SFH 206 K	SFH617A-3X001	SFH6721T	Si1069X-T1-GE3
SFH 213	SFH617A-3X006	SFH6755T	Si1070X-T1-GE3
SFH 229 FA	SFH617A-3X007T	SFH6756T	Si1071X-T1-GE3
SFH 2400 FA	SFH617A-3X016	SFH6757T	Si1317DL-T1-GE3
SFH 2500 FA-Z	SFH617A-3X017T	SFH690CT	Si1403CDL-T1-GE3
SFH 2505 FA-Z	SFH6316T	SFH690C-X001T	Si1416EDH-T1-GE3
SFH6136	SFH6343T	SFT1341-E	Si1469DH-T1-GE3
SFH6136-X001	SFH6700	SFT1341-TL-E	Si2302DS
SFH6136-X006	SFH6700-X009	SFT1345-H	Si2304DS
SFH6136-X007	SFH6701	SFT1345-TL-H	Si2372DS-T1-GE3
SFH6136-X009T	SFH6701-X007	SFT1423-E	Si2374DS-T1-GE3
SFH6136-X016	SFH6701-X009	SFT1423-TL-E	Si5936DU-T1-GE3
SFH6136-X017T	SFH6702	SFT1440-E	Si7121ADN-T1-GE3
SFH6136-X018	SFH6702-X006	SFT1440-H	Si7149ADP-T1-GE3
SFH6136-X019T	SFH6702-X007	SFT1440-TL-E	Si7456CDP-T1-GE3
SFH6156-3	SFH6702-X009T	SFT1440-TL-H	Si8406DB-T2-E1
SFH6156-3T	SFH6705	SGL41-40-E3/96	Si8416DB-T2-E1
SFH615A-3	SFH6705-X006	SHIFT_4BIDI	Si8424CDB-T1-E1
SFH615A-3X001	SFH6705-X007	SHIFT_4PIPO	Si8425DB-T1-E1
SFH615A-3X006	SFH6711	SHIFT_8PIN	Si8461DB-T2-E1
SFH615A-3X007T	SFH6711-X007	SHIFT_8POUT	Si8469DB-T2-E1
SFH615A-3X009T	SFH6712	Shift_Register_74LS 165N	Si8483DB-T2-E1
SFH615A-3X016	SFH6712-X007		Si8487DB-T1-E1

# Multisim 14.0 Education Components

---

Si8497DB-T2-E1	SiR640ADP-T1-GE3	SM15T18A-E3/57T	SM8S36AHE3/2D
Si8499DB-T2-E1	SiR644DP-T1-GE3	SM15T24A-E3/9AT	SM8S43AHE3/2D
Si8800EDB-T2-E1	SiR880ADP-T1-GE3	SM15T33A-E3/57T	SMA5J28A-E3/61
Si8802DB-T2-E1	SiS435DNT-T1-GE3	SM15T68A-E3/57T	SMAJ11A-E3/61
Si8851EDB-T2-E1	SiS439DNT-T1-GE3	SM15T68CA-E3/57T	SMAJ11CA-E3/61
SiA413ADJ-T1-GE3	SiS443DN-T1-GE3	SM3G45	SMAJ12A-E3/61
SiA437DJ-T1-GE3	SiS990DN-T1-GE3	SM3J45	SMAJ12CA-E3/61
SiA440DJ-T1-GE3	SiSA14DN-T1-GE3	SM5S20AHE3/2D	SMAJ150CA-E3/61
SiA446DJ-T1-GE3	SJ1-3515N	SM5S22AHE3/2D	SMAJ15A-E3/61
SiA462DJ-T1-GE3	SL05T1G	SM5S26AHE3/2D	SMAJ16A-E3/61
SiA906EDJ-T1-GE3	SL12-E3/5AT	SM5S33AHE3/2D	SMAJ24A-E3/61
SiA914ADJ-T1-GE3	SL13-E3/61T	SM5S36AHE3/2D	SMAJ24CA-E3/61
SiA922EDJ-T1-GE3	SL22-E3/52T	SM6S33AHE3/2D	SMAJ26A-E3/61
SiA931DJ-T1-GE3	SL23-E3/52T	SM6T12A-E3/52	SMAJ28CA-E3/61
SiA936EDJ-T1-GE3	SL43-E3/57T	SM8S12AHE3/2D	SMAJ36A-E3/61
SiHB23N60E-GE3	SL44-E3/57T	SM8S14AHE3/2D	SMAJ40CA-E3/61
SiHB33N60E-GE3	SLOW_1A	SM8S15AHE3/2D	SMAJ530-E3/61
SiHF23N60E-GE3	SLOW_2A	SM8S16AHE3/2D	SMAJ6.5A-E3/61
SiHG33N60E-GE3	SLOW_3A	SM8S17AHE3/2D	SMAJ60A-E3/61
SiHG64N65E-GE3	SLOW_4A	SM8S18AHE3/2D	SMB8J28CA-E3/52
SiHG73N60E-GE3	SM05T1G	SM8S22AHE3/2D	SMBJ14A-E3/52
SiHP33N60E-GE3	SM12T1G	SM8S24AHE3/2D	SMBJ15CA-E3/52
SiJ470DP-T1-GE3	SM15T150A-E3/57T	SM8S26AHE3/2D	SMBJ170A-E3/52
SiJ478DP-T1-GE3	SM15T150CA-E3/9AT	SM8S30AHE3/2D	SMBJ188CA-E3/52
SiR472ADP-T1-GE3		SM8S33AHE3/2D	SMBJ22A-E3/52



# Multisim 14.0 Education Components

---

SMBJ24CA-E3/52	SMBT3904	SMCJ15A-E3/57T	SMF24AT1G
SMBJ26CA-E3/52	SMBT3906	SMCJ15CA-E3/57T	SMF24CT1G
SMBJ28CA-E3/52	SMBT3906S	SMCJ16CA-E3/57T	SMF26AT1G
SMBJ30A-E3/52	SMBT3946DW1T1G	SMCJ18A-E3/57T	SMF28AT1G
SMBJ33A-E3/52	SMBT4124	SMCJ18CA-E3/57T	SMF30AT1G
SMBJ33CA-E3/52	SMBT4126	SMCJ26CA-E3/57T	SMF33AT1G
SMBJ36A-E3/52	SMBT4401	SMCJ28CA-E3/57T	SMF36AT1G
SMBJ36CA-E3/52	SMBT4403	SMCJ30CA-E3/57T	SMF48AT1G
SMBJ3V3-E3/52	SMBT5086	SMCJ33CA-E3/57T	SMF5.0AT1G
SMBJ45A-E3/52	SMBT5087	SMCJ36CA-E3/57T	SMF58AT1G
SMBJ48A-E3/52	SMBT6428	SMCJ48CA-E3/57T	SMF6.0AT1G
SMBJ48CA-E3/52	SMBT6429	SMCJ5.0CA-E3/57T	SMF6.5AT1G
SMBJ5.0CA-E3/52	SMBTA05	SMCJ51CA-E3/57T	SMF7.0AT1G
SMBJ58A-E3/52	SMBTA06	SMCJ58A-E3/57T	SMF7.5AT1G
SMBJ58CA-E3/52	SMBTA20	SMCJ6.5A-E3/57T	SMF8.0AT1G
SMBJ6.0A-E3/52	SMBTA42	SMCJ75A-E3/57T	SML4735
SMBJ70A-E3/52	SMBTA43	SMCJ78A-E3/57T	SML4736
SMBJ8.0A-E3/52	SMBTA55	SMCJ8.5A-E3/57T	SML4737
SMBJ8.0CA-E3/52	SMBTA56	SMF05CT1G	SML4738
SMBJ85A-E3/52	SMBTA56C	SMF05CT2G	SML4739
SMBT2222A	SMBTA70	SMF12AT1G	SML4740
SMBT2907	SMBTA92	SMF12CT1G	SML4741
SMBT2907A	SMBTA93	SMF15CT1G	SML4742
SMBT35200MT1G	SMCJ12A-E3/57T	SMF18AT1G	SML4743
SMBT3903	SMCJ130CA-E3/57T	SMF22AT1G	SML4744

# Multisim 14.0 Education Components

---

SML4745	SMMBT2222ALT1G	SMMSD4148T1G	SMUN2216T1G
SML4746	SMMBT2222ALT3G	SMMSD4148T3G	SMUN2230T1G
SML4747	SMMBT2369ALT1G	SMMUN2111LT1G	SMUN2232T1G
SML4748	SMMBT2907ALT1G	SMMUN2111LT3G	SMUN2240T1G
SML4749	SMMBT2907ALT3G	SMMUN2113LT1G	SMUN5112DW1T1 G
SML4750	SMMBT3904LT1G	SMMUN2114LT1G	SMUN5112T1G
SML4751	SMMBT3904TT1G	SMMUN2116LT1G	SMUN5113DW1T1 G
SML4752	SMMBT4401LT1G	SMMUN2116LT3G	SMUN5113T1G
SML4753	SMMBT4403LT1G	SMMUN2134LT1G	SMUN5114DW1T1 G
SML4754	SMMBT5401LT1G	SMMUN2211LT1G	SMUN5114T1G
SML4755	SMMBT5551LT1G	SMMUN2211LT3G	SMUN5115DW1T1 G
SML4756	SMMBT5551LT3G	SMMUN2213LT1G	SMUN5115T1G
SML4757	SMMBTA06LT1G	SMMUN2213LT3G	SMUN5116DW1T1 G
SML4758	SMMBTA06LT3G	SMMUN2214LT1G	SMUN5116T1G
SML4759	SMMBTA06WT1G	SMMUN2215LT1G	SMUN5133T1G
SML4760	SMMBTA14LT1G	SMMUN2216LT1G	SMUN5211T1G
SML4761	SMMBTA42LT1G	SMMUN2216LT3G	SMUN5211T3G
SML4762	SMMBTA42LT3G	SMMUN2233LT1G	SMUN5212T1G
SML4763	SMMBTA56LT1G	SMMUN2234LT1G	SMUN5213DW1T1 G
SMMBD2837LT1G	SMMBTA56LT3G	SMS05T1G	SMUN5213T1G
SMMBD301LT3G	SMMBTA92LT1G	SMUN2111T1G	SMUN5214DW1T1 G
SMMBD7000LT1G	SMMBTA92LT3G	SMUN2111T3G	SMUN5214T1G
SMMBD7000LT3G	SMMDL914T1G	SMUN2114T1G	
SMMBD914LT1G	SMMJT350T1G	SMUN2211T1G	
SMMBD914LT3G	SMMSD301T1G	SMUN2211T3G	

# Multisim 14.0 Education Components

---

SMUN5215T1G	SN10502DGK	SPA08N50C3	SPB11N60S5
SMUN5216DW1T1	SN10502DGN	SPA08N80C3	SPB12N50C3
G	SN200501036DRE4	SPA11N60C3	SPB16N50C3
SMUN5230DW1T1	SN412008DRE4	SPA11N60CFD	SPB17N80C3
G	SN7002N	SPA11N80C3	SPB18P06P G
SMUN5232DW1T1	SN7002W	SPA12N50C3	SPB20N60C3
G	SN74121N	SPA15N60C3	SPB20N60S5
SMUN5232T1G	SN74123D	SPA15N60CFD	SPB21N50C3
SMUN5233DW1T1	SN74123FK	SPA16N50C3	SPB80P06P G
G	SN74123N	SPA17N80C3	SPD01N60C3
SMUN5233T1G	SN74130N	SPA20N60C3	SPD02N50C3
SMUN5235DW1T1	SNSS30201MR6T1G	SPA20N60CFD	SPD02N60C3
G	SNSS35200MR6T1G	SPA21N50C3	SPD02N60S5
SMUN5311DW1T2	SNSS40600CF8T1G	SPB02N60C3	SPD02N80C3
G	SNUF6401MNT1G	SPB02N60S5	SPD03N50C3
SMUN5312DW1T1	SONALERT	SPB03N60C3	SPD03N60C3
G	SPA02N80C3	SPB03N60S5	SPD03N60S5
SMUN5313DW1T1	SPA03N60C3	SPB04N50C3	SPD04N50C3
G	SPA04N50C3	SPB04N60C3	SPD04N60C3
SMUN5314DW1T1	SPA04N60C3	SPB04N60S5	SPD04N60S5
G	SPA04N80C3	SPB07N60C3	SPD04N80C3
SMUN5315DW1T1	SPA06N60C3	SPB07N60S5	SPD04P10PL G
G	SPA06N80C3	SPB08P06P G	SPD06N60C3
SMUN5330DW1T1	SPA07N60C3	SPB100N03S2-03 G	SPD06N80C3
G	SPA07N60CFD	SPB11N60C3	SPD07N60C3
SMUN5335DW1T1			
G			
SN10502D			

# Multisim 14.0 Education Components

---

SPD07N60S5	SPI11N60S5	SPP11N60C3	SPST_OPEN
SPD08N50C3	SPI12N50C3	SPP11N60CFD	SPU01N60C3
SPD08P06P G	SPI15N60C3	SPP11N60S5	SPU02N60C3
SPD09P06PL G	SPI15N60CFD	SPP11N80C3	SPU02N60S5
SPD15P10P G	SPI16N50C3	SPP12N50C3	SPU03N60C3
SPD15P10PL G	SPI20N60C3	SPP15N60C3	SPU03N60S5
SPD18P06P G	SPI20N60CFD	SPP15N60CFD	SPU04N60C3
SPD30N03S2L-07 G	SPI21N50C3	SPP15P10P H	SPU04N60S5
SPD30N03S2L-10 G	SPP02N60C3	SPP15P10PL H	SPU07N60C3
SPD30N03S2L-20 G	SPP02N60S5	SPP16N50C3	SPU07N60S5
SPD30P06P G	SPP02N80C3	SPP17N80C3	SPW07N60CFD
SPD50N03S2-07 G	SPP03N60C3	SPP18P06P H	SPW11N60C3
SPD50N03S2L-06 G	SPP03N60S5	SPP20N60C3	SPW11N60CFD
SPD50P03L G	SPP04N50C3	SPP20N60CFD	SPW11N60S5
SPDT	SPP04N60C3	SPP20N60S5	SPW11N80C3
SPDT_CLOSED	SPP04N60S5	SPP21N50C3	SPW12N50C3
SPDT_OPEN	SPP04N80C3	SPP24N60C3	SPW15N60C3
SPEED_F	SPP06N60C3	SPP24N60CFD	SPW15N60CFD
SPEED_FR	SPP06N80C3	SPP80P06P H	SPW16N50C3
SPI07N60C3	SPP07N60C3	SPST	SPW17N80C3
SPI07N60S5	SPP07N60CFD	SPST_CLOSED	SPW20N60C3
SPI08N50C3	SPP07N60S5	SPST_NC_DB	SPW20N60CFD
SPI08N80C3	SPP08N50C3	SPST_NC_SB	SPW20N60S5
SPI11N60C3	SPP08N80C3	SPST_NO_DB	SPW21N50C3
SPI11N60CFD	SPP08P06P H	SPST_NO_SB	SPW24N60C3

# Multisim 14.0 Education Components

---

SPW24N60CFD	SR_LATCH	SS2P4-M3/84A	SSM2212RZ-R7
SPW32N50C3	SR_LATCH_NEGSR	SS2PH10-M3/84A	SSM2212RZ-RL
SPW35N60C3	SS0503SH-TL-E	SS32	SSRD8620CTRG
SPW35N60CFD	SS10P3-M3/86A	SS32-E3/57T	SSRD8620CTT4G
SPW47N60C3	SS10P4-M3/86A	SS33	SSRD8620CTT4RG
SPW47N60CFD	SS10P6-M3/86A	SS34	ST5771-1
SPW52N50C3	SS10PH10-M3/86A	SS34-E3/57T	STD110N02RT4G
SPZT2222AT1G	SS14-E3/61T	SS35	STD24N06LT4G
SPZT2907AT1G	SS16-E3/61T	SS36-E3/57T	STD2955T4G
SPZT651T1G	SS16T3G	SS3P4HM3/84A	STD5406NT4G
SQJ461EP-T1-GE3	SS1H10-E3/5AT	SS3P4LHM3/86A	STD5407NT4G
SQS482EN-T1-GE3	SS1P3L-M3/84A	SS3P6-E3/84A	STEP_CURRENT
SR_4BIDI	SS1P4L-M3/84A	SS5P10-M3/86A	STEP_VOLTAGE
SR_4P_P_3SO	SS1P4-M3/84A	SS5P6-M3/86A	STEPPER_FULLSTEP _2PHASE
SR_4P_P_INV	SS1P6L-E3/84A	SS8P3L-M3/86A	STEPPER_HALFSTEP _2PHASE
SR_4S_P	SS22T3G	SS8PH10-M3/86A	STEPPER_MOTOR_ 2PHASE
SR_8P_2S	SS24-E3/52T	SSA24-E3/61T	STEPPER_MOTOR_ 2PHASE_2WINDING
SR_8P_S	SS24S-E3/61T	SSA33L-E3/61T	STEPPER_WAVE_2P HASE
SR_8P_S_C	SS24T3	SSA34-E3/61T	STF202-22T1G
SR_8PS_S_AS_L	SS24T3G	SSC53L-E3/57T	STP32N06L
SR_8PS_S_SL	SS26-E3/52T	SSC54-E3/57T	SUD17N25-165-E3
SR_8S_P	SS26T3	SSM2017P	SUR620CTT4G
SR_FF	SS26T3G	SSM2017S	
SR_FF_NEGSR	SS2H10-E3/2CT	SSM2135S	
SR_FF_POSSR	SS2P3L-M3/84A	SSM2212RZ	

# Multisim 14.0 Education Components

---

SUR81520G	SURS360DT3G	SYNCHRONOUS_M	SZ1SMB24CAT3G
SUR81560G	SURS8105T3G	ACHINE_PERMANE	SZ1SMB26CAT3G
		NT_MAGNET	
SUR83020PTG	SURS8110T3G	SYNCHRONOUS_M	SZ1SMB28AT3G
SUR83060PTG	SURS8115T3G	ACHINE_PERMANE	SZ1SMB28CAT3G
		NT_MAGNET_E	
SUR8820G	SURS8120T3G	SYNCHRONOUS_M	SZ1SMB30AT3G
SUR8840G	SURS8140T3G	ACHINE_PERMANE	SZ1SMB30CAT3G
		NT_MAGNET_HALL	
SURA8110T3G	SURS8160T3G		SZ1SMB33CAT3G
SURA8120T3G	SURS8205T3G	SZ1.5SMC15AT3G	SZ1SMB5.0AT3G
SURA8130T3G	SURS8210T3G	SZ1.5SMC20AT3G	SZ1SMB58CAT3G
SURA8140T3G	SURS8220T3G	SZ1.5SMC33AT3G	SZ1SMB5918BT3G
SURA8160T3G	SURS8320T3G	SZ1.5SMC39AT3G	SZ1SMB5919BT3G
SURA8210T3G	SURS8340T3G	SZ1.5SMC43AT3G	SZ1SMB5920BT3G
SURA8215T3G	SURS8360BT3G	SZ1.5SMC62AT3G	SZ1SMB5921BT3G
SURA8220T3G	SURS8360T3G	SZ1SMA30AT3G	SZ1SMB5922BT3G
SURA8240T3G	SWHYSTE	SZ1SMA40CAT3G	SZ1SMB5924BT3G
SURB1620CTT4G	Switch1	SZ1SMA5913BT3G	SZ1SMB5925BT3G
SURD8320T4G	SXT2222A	SZ1SMA5918BT3G	SZ1SMB5927BT3G
SURD8330T4G	SXT2907A	SZ1SMA5921BT3G	SZ1SMB5931BT3G
SURD8530T4G	SXT3904	SZ1SMA5922BT3G	SZ1SMB5933BT3G
SURHB8840CTT4G	SXT3906	SZ1SMA5927BT3G	SZ1SMB5934BT3G
SURHD8560T4G	SXTA42	SZ1SMA5932BT3G	SZ1SMB5935BT3G
SURHD8560W1T4G	SXTA43	SZ1SMA5936BT3G	SZ1SMB5936BT3G
SURHS8160T3G	SXTA92	SZ1SMA5940BT3G	SZ1SMB5937BT3G
SURS340DT3G	SXTA93	SZ1SMB14AT3G	SZ1SMB5939BT3G
SURS360DBT3G		SZ1SMB24AT3G	SZ1SMC36AT3G

# Multisim 14.0 Education Components

---

SZBZX84B16LT1G	SZMM3Z10VT1G	SZMM5Z5V1T1G	SZMMBZ5240BLT1G
SZBZX84C12LT1G	SZMM3Z12VST1G	SZMM5Z5V6ST1G	SZMMBZ5242BLT1G
SZBZX84C15LT1G	SZMM3Z15VT1G	SZMM5Z5V6T1G	SZMMBZ5248BLT1G
SZBZX84C15LT3G	SZMM3Z18VT1G	SZMM5Z6V2ST1G	SZMMBZ5254BLT1G
SZBZX84C33LT1G	SZMM3Z20VT1G	SZMM5Z6V8ST1G	SZMMBZ5256BLT1G
SZBZX84C33LT3G	SZMM3Z2V4T1G	SZMM5Z6V8T1G	SZMMBZ5256BLT1G
SZBZX84C36LT1G	SZMM3Z3V3ST1G	SZMM5Z7V5T1G	SZMMBZ5256BLT1G
SZBZX84C3V0LT1G	SZMM3Z3V6T1G	SZMM5Z8V2ST1G	SZMMBZ5V6ALT1G
SZBZX84C4V7LT1G	SZMM3Z43VT1G	SZMM5Z8V2T1G	SZMMQA15VT1G
SZBZX84C4V7LT3G	SZMM3Z4V3ST1G	SZMMBZ15VDLT1G	SZMMQA5V6T1G
SZBZX84C5V1LT1G	SZMM3Z4V7T1G	SZMMBZ15VDLT3G	SZMMQA6V2T1G
SZBZX84C5V1LT3G	SZMM3Z5V1T1G	SZMMBZ20VALT1G	SZMMSZ10T1G
SZBZX84C5V6LT1G	SZMM3Z5V6ST1G	SZMMBZ27VALT1G	SZMMSZ12T1G
SZBZX84C5V6LT3G	SZMM5Z10VT1G	SZMMBZ27VALT3G	SZMMSZ2V7T1G
SZBZX84C68LT1G	SZMM5Z12VT1G	SZMMBZ27VCLT1G	SZMMSZ3V3T1G
SZBZX84C6V2LT1G	SZMM5Z16VT1G	SZMMBZ33VALT1G	SZMMSZ4678T1G
SZBZX84C6V2LT3G	SZMM5Z18VT1G	SZMMBZ5221BLT1G	SZMMSZ4683T1G
SZBZX84C6V8LT1G	SZMM5Z20VT1G	SZMMBZ5222BLT1G	SZMMSZ4688T1G
SZBZX84C6V8LT3G	SZMM5Z24VT1G	SZMMBZ5231BLT1G	SZMMSZ4689T1G
SZBZX84C75LT1G	SZMM5Z27VT1G	SZMMBZ5231BLT3G	SZMMSZ4690T1G
SZBZX84C9V1LT1G	SZMM5Z36VT1G	SZMMBZ5232BLT1G	SZMMSZ4690T3G
SZBZX84C9V1LT3G	SZMM5Z3V0T1G	SZMMBZ5232BLT1G	SZMMSZ4691T1G
SZESD5Z5.0T1G	SZMM5Z3V3T1G	SZMMBZ5232BLT1G	SZMMSZ4692T1G
SZESD5Z7.0T1G	SZMM5Z4V7ST1G		SZMMSZ4696T1G
SZESD9B5.0ST5G	SZMM5Z4V7ST5G		

# Multisim 14.0 Education Components

---

SZMMSZ4699T1G	SZNUP1105LT1G	TC1410EOA	TC1412COA
SZMMSZ4705T1G	SZNUP1301ML3T1G	TC1410EPA	TC1412CPA
SZMMSZ4715T1G	SZNUP2105LT1G	TC1410EUA	TC1412EOA
SZMMSZ5221BT1G	SZNUP4301MR6T1 G	TC1410NCOA	TC1412EPA
SZMMSZ5225BT1G		TC1410NCPA	TC1412EUA
SZMMSZ5226BT1G	SZNUP4304MR6T1 G	TC1410NEOA	TC1412NCOA
SZMMSZ5228BT1G	SZNZ9F2V7ST5G	TC1410NEPA	TC1412NCPA
SZMMSZ5231BT1G	SZNZ9F6V2ST5G	TC1410NEUA	TC1412NEOA
SZMMSZ5234BT1G	SZP6SMB15AT3G	TC1410NVUA	TC1412NEPA
SZMMSZ5235BT1G	SZP6SMB18AT3G	TC1411COA	TC1412NEUA
SZMMSZ5236BT1G	SZP6SMB20AT3G	TC1411CPA	TC4404COA
SZMMSZ5239BT1G	SZP6SMB33AT3G	TC1411EOA	TC4404CPA
SZMMSZ5240BT1G	SZP6SMB43CAT3G	TC1411EPA	TC4404EOA
SZMMSZ5242BT1G	SZP6SMB51AT3G	TC1411EUA	TC4404EPA
SZMMSZ5242BT3G	SZP6SMB6.8AT3G	TC1411NCOA	TC4405COA
SZMMSZ5243BT1G	SZP6SMB62AT3G	TC1411NCPA	TC4405CPA
SZMMSZ5245BT1G	SZSMF12CT1G	TC1411NEOA	TC4405EOA
SZMMSZ5246BT1G	SZSMF33AT1G	TC1411NEPA	TC4405EPA
SZMMSZ5254BT1G	T_FF	TC1411NEUA	TC4420CAT
SZMMSZ5258BT1G	T_FF_NEGSR	TC1411NVOA	TC4420COA
SZMMSZ5258BT3G	TBASE_TIMER_TOF F	TC1411NVPA	TC4420CPA
SZMMSZ5259BT1G		TC1411NVUA	TC4420EMF
SZMMSZ5260BT1G	TBASE_TIMER_TON	TC1411VOA	TC4420EOA
SZMMSZ5262BT1G	TC1410COA	TC1411VPA	TC4420EPA
SZMSQA6V1W5T2G	TC1410CPA	TC1411VUA	TC4420IJA



# Multisim 14.0 Education Components

---

TC4420MJA	TC4423AVOA	TC4425AVOA	TC4427EMF
TC4420VAT	TC4423AVOE	TC4425AVOE	TC4427EOA
TC4420VMF	TC4423AVPA	TC4425AVPA	TC4427EPA
TC4420VOA	TC4423COE	TC4425COE	TC4427EUA713
TC4420VPA	TC4423CPA	TC4425CPA	TC4427VMF
TC4421AVMF	TC4423EOE	TC4425EOE	TC4427VOA
TC4421CAT	TC4423EPA	TC4425EPA	TC4427VUA
TC4421CPA	TC4423MJA	TC4425VMF	TC4428ACOA713
TC4421EMF713	TC4423VMF	TC4425VOE	TC4428AEJA
TC4421EPA	TC4423VOE	TC4425VPA	TC4428AEOA713
TC4421ESM	TC4423VPA	TC4426ACOA713	TC4428AMJA
TC4421MJA	TC4424AVMF	TC4426AEOA713	TC4428COA
TC4421VAT	TC4424AVOA	TC4426COA	TC4428CPA
TC4421VMF	TC4424AVOE	TC4426CPA	TC4428EMF
TC4421VPA	TC4424AVPA	TC4426EMF	TC4428EOA
TC4422CAT	TC4424COE	TC4426EOA	TC4428EPA
TC4422CPA	TC4424CPA	TC4426EPA	TC4428EUA
TC4422EAT	TC4424EMF	TC4426EUA	TC4428VMF
TC4422EPA	TC4424EOE	TC4426MJA	TC4428VOA
TC4422ESM	TC4424EPA	TC4426VMF	TC4428VUA
TC4422MJA	TC4424MJA	TC4426VUA	TC4429COA713
TC4422VAT	TC4424VMF	TC4427ACOA713	TC4429EMF
TC4422VMF	TC4424VOE	TC4427AEOA713	TC4429EOA713
TC4422VPA	TC4424VPA	TC4427COA	TC4429IJA
TC4423AVMF	TC4425AVMF	TC4427CPA	TC4429MJA

# Multisim 14.0 Education Components

---

TC4429VAT	TC4467CPD	TDZ11J	TDZ9V1J
TC4429VMF	TC4467EOE713	TDZ12J	TEMMD1000
TC4429VOA	TC4468COE	TDZ13J	TEMMD1020
TC4429VPA	TC4468CPD	TDZ15J	TEMMD1030
TC4431COA	TC4468EOE713	TDZ16J	TEMMD5010X01
TC4431CPA	TC4468MOE	TDZ18J	TEMMD5020X01
TC4431EOA	TC4469COE	TDZ20J	TEMMD5110X01
TC4431EPA	TC4469CPD	TDZ22J	TEMMD5510FX01
TC4431VOA	TC4469EJD	TDZ24J	TEMMD6010FX01
TC4431VPA	TC4469MJD	TDZ27J	TEMP_NC
TC4432COA	TCET1100	TDZ2V4J	TEMP_NO
TC4432CPA	TCET1100G	TDZ2V7J	TEMPERATURE_SO URCE
TC4432EOA	TCET1600	TDZ30J	TEMPLATE_1P1S_T MODEL
TC4432EPA	TCET1600G	TDZ3V0J	TEMPLATE_1P2S_C OUPLED
TC4432VOA	TCLT1003	TDZ3V3J	TEMPLATE_1P2S_N ON_LINEAR
TC4432VPA	TCMT1103	TDZ3V6J	TEMPLATE_1P2S_T AP_TMODEL
TC4451VAT	TCMT1600	TDZ3V9J	TEMPLATE_1P2S_T MODEL
TC4451VMF	TCMT4600	TDZ4V3J	TEST_LABEL
TC4451VOA	TD_SW1	TDZ4V7J	TEST_PT_SMT
TC4451VPA	TD4A	TDZ5V1J	TEST_PT_THT
TC4452VAT	TD5A	TDZ5V6J	THERMAL_NOISE
TC4452VMF	TDA2030	TDZ6V2J	
TC4452VOA	TDM_CURRENT	TDZ6V8J	
TC4452VPA	TDM_VOLTAGE	TDZ7V5J	
TC4467COE	TDZ10J	TDZ8V2J	

# Multisim 14.0 Education Components

---

THERMAL_OL	THS3111ID	THS4011CDGN	THS4041CDGN
THERMAL_OL_RELAY	THS3111IDGN	THS4011ID	THS4041ID
THREE_PHASE_DELTA	THS3120CDGN	THS4011MFKB	THS4041IDGN
THREE_PHASE_WYE	THS3120DGN	THS4012CD	THS4042CD
THS3001CD	THS3120ID	THS4012CDGN	THS4042CDGN
THS3001CDGN	THS3120IDGN	THS4012ID	THS4042ID
THS3001ID	THS3121CD	THS4021CD	THS4042IDGN
THS3001IDGN	THS3121ID	THS4021CDGN	THS4051CD
THS3061D	THS3121IDGN	THS4021ID	THS4051CDGN
THS3061DGN	THS3122CD	THS4021IDGN	THS4051ID
THS3062D	THS3122CDDA	THS4022CD	THS4051IDGN
THS3062DDA	THS3122ID	THS4022CDGN	THS4051MFK
THS3062DGN	THS3122IDDA	THS4022ID	THS4051MJG
THS3091D	THS3125CPWP	THS4022IDGN	THS4052CD
THS3091DDA	THS3125ID	THS4031CD	THS4052CDGN
THS3095D	THS3125IPWP	THS4031CDGN	THS4052ID
THS3095DDA	THS3201D	THS4031ID	THS4052IDGN
THS3110DGN	THS3201DBVT	THS4031IDGN	THS4061CD
THS3110ID	THS3201DGK	THS4031MFK	THS4061CDGN
THS3110IDGN	THS3202D	THS4031MJG	THS4061ID
THS3110IDR	THS3202DGK	THS4032CD	THS4061IDGN
THS3111CD	THS3202DGN	THS4032CDGN	THS4061MFK
THS3111CDGNR	THS4001CD	THS4032ID	THS4061MJG
THS3111DGN	THS4001ID	THS4032IDGN	THS4062CD
	THS4011CD	THS4041CD	THS4062CDGN

# Multisim 14.0 Education Components

---

THS4062ID	THS4140IDGK	THS4222DGK	THS4501CD
THS4062IDGN	THS4141CD	THS4222DGN	THS4501CDGK
THS4081CD	THS4141CDGK	THS4225D	THS4501CDGN
THS4081CDGN	THS4141ID	THS4225DGK	THS4501ID
THS4081ID	THS4141IDGK	THS4225DGN	THS4501IDGK
THS4081IDGN	THS4150CD	THS4226DGQ	THS4501IDGN
THS4082CD	THS4150CDGK	THS4271D	THS4502CD
THS4082CDGN	THS4150ID	THS4271DGK	THS4502CDGK
THS4082ID	THS4150IDGK	THS4271DGN	THS4502ID
THS4082IDGN	THS4151CD	THS4271DR	THS4502IDGK
THS4120CD	THS4151CDGK	THS4271DRBT	THS4503CD
THS4120CDGK	THS4151ID	THS4281D	THS4503CDGK
THS4121CD	THS4151IDGK	THS4281DBVR	THS4503CDGN
THS4121CDGK	THS4211D	THS4281DGK	THS4503ID
THS4130CD	THS4211DGK	THS4302RGTT	THS4503IDGK
THS4130CDGK	THS4211DGN	THS4303RGTT	THS4503IDGN
THS4130ID	THS4215D	THS4304D	THS4505D
THS4130IDGK	THS4215DGK	THS4304DBVT	THS4505DGK
THS4131CD	THS4215DGN	THS4304DGK	THS4508RGTR
THS4131CDGK	THS4215DRBT	THS4500CD	THS4509RGT
THS4131ID	THS4221D	THS4500CDGK	THS4511RGTT
THS4131IDGK	THS4221DBV	THS4500CDGN	THS4513RGTR
THS4140CD	THS4221DGK	THS4500ID	THS4520RGTR
THS4140CDGK	THS4221DGN	THS4500IDGK	THS4601CD
THS4140ID	THS4222D	THS4500IDGN	THS4601CDDA

# Multisim 14.0 Education Components

---

THS4601CDG4	THS6052CD	THS6184PWP	TIMER_TON_RETEN TION_HOLD_RESET
THS4601ID	THS6052CDDA	THS6184RHFR	
THS4601IDDA	THS6052ID	THS7001CPWP	TIMER_TON_RETEN TION_RESET
THS4601IDG4	THS6052IDDA	THS7001IPWP	TI-MSP430-HDR
THS4631D	THS6053CPWPR	THS7002CPWP	TIP100G
THS4631DDA	THS6053ID	THS7002IPWP	TIP101G
THS4631DGN	THS6053IPWP	THS7530PWP	TIP102G
THS6002CDWP	THS6062CD	TIME_DELAY_1A	TIP106G
THS6002IDWP	THS6062CDGN	TIME_DELAY_1C	TIP107G
THS6007IPWP	THS6062ID	TIME_DELAY_2A	TIP110G
THS6012CDWP	THS6062IDGN	TIME_DELAY_2C	TIP111G
THS6012IDWP	THS6072CD	TIME_DELAY_3A	TIP112G
THS6012IGQER	THS6072CDGN	TIME_DELAY_3C	TIP115G
THS6022CPWP	THS6072ID	TIME_DELAY_4A	TIP116G
THS6022IPWP	THS6072IDGNR	TIME_DELAY_4C	TIP117G
THS6032CDWP	THS6092CDDA	TIME_DELAY_NC	TIP120G
THS6032IDWP	THS6092ID	TIME_DELAY_NO	TIP121G
THS6032IVFPG4	THS6092IDDA	TIMED_NCTC	TIP122G
THS6042CDDA	THS6093CPWP	TIMED_NCTO	TIP125G
THS6042ID	THS6093ID	TIMED_NOTC	TIP126G
THS6042IDDA	THS6093IPWP	TIMED_NOTO	TIP127G
THS6043CD	THS6182D	TIMER_TOFF	TIP140G
THS6043CPWP	THS6182DW	TIMER_TON	TIP141G
THS6043ID	THS6182DWP	TIMER_TON_RETEN TION	TIP142G
THS6043IPWP	THS6182RHFR		TIP147G

# Multisim 14.0 Education Components

---

TIP2955G	TIP42G	TL031MFK	TL034AMD
TIP29AG	TIP47G	TL031MJG	TL034AMFK
TIP29BG	TIP48G	TL031MP	TL034AMJ
TIP29CG	TIP50G	TL032ACD	TL034AMN
TIP3055G	TIS92	TL032ACP	TL034CD
TIP30CG	TIS93	TL032AID	TL034CN
TIP31AG	TIS97	TL032AIP	TL034ID
TIP31BG	TIS98	TL032AMD	TL034IN
TIP31CG	TIS99	TL032AMFK	TL034MD
TIP31G	TL022CD	TL032AMJG	TL034MFK
TIP32AG	TL022CP	TL032AMJL	TL034MJ
TIP32BG	TL022MJG	TL032AMP	TL034MN
TIP32CG	TL022MU	TL032CD	TL044CJ
TIP32G	TL031ACD	TL032CP	TL044CN
TIP33CG	TL031ACP	TL032ID	TL044MFK
TIP35AG	TL031AID	TL032IP	TL044MJ
TIP35CG	TL031AIP	TL032MD	TL044MW
TIP36AG	TL031AMD	TL032MFK	TL051ACD
TIP36CG	TL031AMFK	TL032MJG	TL051ACP
TIP41AG	TL031AMJG	TL032ML	TL051AID
TIP41BG	TL031AML	TL032MP	TL051AIP
TIP41CG	TL031AMP	TL034ACD	TL051AMD
TIP42AG	TL031ID	TL034ACN	TL051AMFK
TIP42BG	TL031IP	TL034AID	TL051AMJG
TIP42CG	TL031MD	TL034AIN	TL051AML

# Multisim 14.0 Education Components

---

TL051AMP	TL052MJG	TL061ID	TL064ACN
TL051CD	TL052ML	TL061IP	TL064BCD
TL051CP	TL052MP	TL061MFK	TL064BCN
TL051ID	TL054ACD	TL061MJG	TL064CD
TL051IP	TL054ACN	TL061ML	TL064CN
TL051MD	TL054AID	TL061MU	TL064CNSR
TL051MFK	TL054AIN	TL061VD	TL064CPW
TL051MJG	TL054AMD	TL061VP	TL064ID
TL051ML	TL054AMFK	TL062ACD	TL064IN
TL051MP	TL054AMJ	TL062ACP	TL064MFK
TL052ACD	TL054AMN	TL062ACPSR	TL064MJ
TL052ACP	TL054CD	TL062BCD	TL064MW
TL052AID	TL054CN	TL062BCP	TL066ACD
TL052AIP	TL054ID	TL062CD	TL066ACP
TL052AMD	TL054IN	TL062CP	TL066CD
TL052AMFK	TL054MD	TL062CPSR	TL066CP
TL052AMJG	TL054MFK	TL062CPW	TL066ID
TL052AML	TL054MJ	TL062ID	TL066IP
TL052AMP	TL054MN	TL062IP	TL066MFK
TL052CD	TL061ACD	TL062IPW	TL066MJG
TL052CP	TL061ACP	TL062MFK	TL070ACD
TL052ID	TL061BCD	TL062MJG	TL070ACJG
TL052IP	TL061BCP	TL062ML	TL070ACP
TL052MD	TL061CD	TL062MU	TL070CD
TL052MFK	TL061CP	TL064ACD	TL070CJG

# Multisim 14.0 Education Components

---

TL070CP	TL072BCP	TL074MW	TL082CP
TL070CPW	TL072CD	TL075	TL082ID
TL070ID	TL072CP	TL075CN	TL082IP
TL070IJG	TL072CPSR	TL080CD	TL082IPWR
TL070IP	TL072CPW	TL080CP	TL082MFK
TL070MD	TL072CPWLE	TL080M	TL082MJG
TL070MP	TL072ID	TL081ACD	TL083
TL071ACD	TL072IP	TL081ACJG	TL084ACD
TL071ACJG	TL072MFK	TL081ACP	TL084ACN
TL071ACP	TL072MJG	TL081AMJG	TL084ACNSR
TL071BCD	TL072MJGB	TL081BCD	TL084BCD
TL071BCP	TL072ML	TL081BCJG	TL084BCN
TL071CD	TL072MP	TL081BCP	TL084CD
TL071CJG	TL074ACD	TL081CD	TL084CN
TL071CP	TL074ACN	TL081CJG	TL084CNSR
TL071CPWLE	TL074BCD	TL081CP	TL084CPW
TL071ID	TL074BCN	TL081CPW	TL084ID
TL071IP	TL074CD	TL081ID	TL084IN
TL071MFK	TL074CN	TL081IJG	TL084MFK
TL071MJG	TL074CPWLE	TL081IP	TL084MJ
TL071ML	TL074ID	TL081MFK	TL085
TL072ACD	TL074IN	TL081MJG	TL087CD
TL072ACP	TL074MFK	TL081MU	TL087CJG
TL072ACPSR	TL074MJ	TL082CD	TL087CL
TL072BCD	TL074MN	TL082CM	TL087CP



# Multisim 14.0 Education Components

---

TL087ID	TL288MJG	TL3474ID	TL972IP
TL087IJG	TL288ML	TL3474IN	TL972IPW
TL087IL	TL288MU	TL3474IPW	TLC070CD
TL087IP	TL321CD	TL35071D	TLC070CP
TL088CD	TL321CP	TL35071P	TLC070ID
TL088CJG	TL321ID	TL431ACD	TLC070IP
TL088CL	TL321IP	TL431ACLP	TLC071CD
TL088CP	TL322CD	TL431ACP	TLC071CP
TL088ID	TL322CDR	TL431BCD	TLC071ID
TL088IJG	TL322CP	TL431BCLP	TLC071IP
TL088IL	TL322ID	TL431BCP	TLC074CD
TL088IP	TL322IP	TL431ID	TLC074CN
TL088MJG	TL33071D	TL431IDBVR	TLC074CPWP
TL088ML	TL33071P	TL431IDBZR	TLC081CD
TL088MU	TL331IDBVR	TL431ILP	TLC081CP
TL136	TL331KDBVR	TL431ILPR	TLC081ID
TL136N	TL34071D	TL431IP	TLC081IP
TL287CD	TL34071P	TL431IPK	TLC1078CD
TL287CJG	TL3472CD	TL431QD	TLC1078CP
TL287CL	TL3472CP	TL431QDBVR	TLC1078ID
TL287CP	TL3472ID	TL431QDBZR	TLC1078IP
TL288CD	TL3472IP	TL431QDCKR	TLC1078MD
TL288CJG	TL3474CD	TL431QPK	TLC1078MFK
TL288CL	TL3474CN	TL972ID	TLC1078MJG
TL288CP	TL3474CPW	TL972IDGKR	TLC1078MP

# Multisim 14.0 Education Components

---

TLC1079CD	TLC2202ACD	TLC2252MU	TLC2272Y
TLC1079CN	TLC2202ACP	TLC2254CD	TLC2274ACD
TLC1079ID	TLC2202AID	TLC2254CN	TLC2274ACN
TLC1079IN	TLC2202AIP	TLC2254CPWLE	TLC2274ACPW
TLC1079MD	TLC2202BCD	TLC2254MFK	TLC2274CD
TLC1079MFK	TLC2202BCP	TLC2254MJ	TLC2274CN
TLC1079MJ	TLC2202BID	TLC2254MW	TLC2274CPWLE
TLC1079MN	TLC2202BIP	TLC2262CD	TLC2274MD
TLC2201ACD	TLC2202CD	TLC2262CP	TLC2274MFK
TLC2201ACP	TLC2202CP	TLC2262CPWLE	TLC2274MJ
TLC2201AID	TLC2202ID	TLC2262MFK	TLC2274MN
TLC2201AIP	TLC2202IP	TLC2262MJG	TLC251ACD
TLC2201BCD	TLC2202MD	TLC2262MU	TLC251ACP
TLC2201BCP	TLC2202MFK	TLC2264CD	TLC251BCD
TLC2201BID	TLC2202MJG	TLC2264CN	TLC251BCP
TLC2201BIP	TLC2202MP	TLC2264CPW	TLC251CD
TLC2201CD	TLC2202Y	TLC2264CPWLE	TLC251CP
TLC2201CP	TLC2252AID	TLC2264MFK	TLC251Y
TLC2201ID	TLC2252AIP	TLC2264MJ	TLC252ACD
TLC2201IP	TLC2252AIPWLE	TLC2264MW	TLC252ACP
TLC2201MD	TLC2252CD	TLC2272ACD	TLC252ACPW
TLC2201MFK	TLC2252CP	TLC2272ACP	TLC252BCD
TLC2201MJG	TLC2252CPWLE	TLC2272CD	TLC252BCP
TLC2201MP	TLC2252MFK	TLC2272CP	TLC252BCPW
TLC2201Y	TLC2252MJG	TLC2272CPWLE	TLC252CD

# Multisim 14.0 Education Components

---

TLC252CP	TLC2652AC-14D	TLC2652MFK	TLC2654CP
TLC252CPW	TLC2652AC-8D	TLC2652MJ	TLC2654I-14D
TLC254ACD	TLC2652ACN	TLC2652MJG	TLC2654I-8D
TLC254ACN	TLC2652ACP	TLC2652MN	TLC2654IN
TLC254BCD	TLC2652AI-14D	TLC2652MP	TLC2654IP
TLC254BCN	TLC2652AI-8D	TLC2652Y	TLC2654M-14D
TLC254CD	TLC2652AIN	TLC2654AC-14D	TLC2654M-8D
TLC254CN	TLC2652AIP	TLC2654AC-8D	TLC2654MFK
TLC254CPW	TLC2652AM-14D	TLC2654ACN	TLC2654MJ
TLC25L2ACD	TLC2652AM-8D	TLC2654ACP	TLC2654MJG
TLC25L2ACP	TLC2652AMFK	TLC2654AI-14D	TLC2654MN
TLC25L2BCD	TLC2652AMJ	TLC2654AID	TLC2654MP
TLC25L2BCP	TLC2652AMJG	TLC2654AIN	TLC271ACD
TLC25L2CD	TLC2652AMN	TLC2654AIP	TLC271ACP
TLC25L2CP	TLC2652AMP	TLC2654AM-14D	TLC271AID
TLC25L4CD	TLC2652C-14D	TLC2654AM-8D	TLC271AIP
TLC25L4CN	TLC2652C-8D	TLC2654AMF	TLC271BCD
TLC25M2ACD	TLC2652CN	TLC2654AMFK	TLC271BCP
TLC25M2ACP	TLC2652CP	TLC2654AMJ	TLC271BID
TLC25M2BCD	TLC2652I-14D	TLC2654AMJG	TLC271BIP
TLC25M2BCP	TLC2652ID	TLC2654AMN	TLC271CD
TLC25M2CD	TLC2652IN	TLC2654AMP	TLC271CP
TLC25M2CP	TLC2652IP	TLC2654C-14D	TLC271ID
TLC25M4CD	TLC2652M-14D	TLC2654C-8D	TLC271IP
TLC25M4CN	TLC2652M-8D	TLC2654CN	TLC271MD

# Multisim 14.0 Education Components

---

TLC271MFK	TLC277MD	TLC27L2MFK	TLC27L7MJG
TLC271MJG	TLC277MFK	TLC27L2MJG	TLC27L7MP
TLC271MP	TLC277MJG	TLC27L2MP	TLC27L9CD
TLC272CD	TLC277MP	TLC27L4ACD	TLC27L9CN
TLC272CP	TLC279CD	TLC27L4ACN	TLC27L9ID
TLC272CPW	TLC279CN	TLC27L4AID	TLC27L9IN
TLC272ID	TLC279ID	TLC27L4AIN	TLC27L9MD
TLC272IP	TLC279IN	TLC27L4BCD	TLC27L9MFK
TLC272MD	TLC279MD	TLC27L4BCN	TLC27L9MJ
TLC272MFK	TLC279MFK	TLC27L4BID	TLC27L9MP
TLC272MJG	TLC279MJ	TLC27L4BIN	TLC27M2ACD
TLC272MP	TLC279MN	TLC27L4CD	TLC27M2ACP
TLC274CD	TLC27L2ACD	TLC27L4CN	TLC27M2AID
TLC274CN	TLC27L2ACP	TLC27L4ID	TLC27M2AIP
TLC274CPW	TLC27L2AID	TLC27L4IN	TLC27M2BCD
TLC274ID	TLC27L2AIP	TLC27L4MD	TLC27M2BCP
TLC274IN	TLC27L2BCD	TLC27L4MFK	TLC27M2BID
TLC274MD	TLC27L2BCP	TLC27L4MJ	TLC27M2BIP
TLC274MFK	TLC27L2BID	TLC27L4MN	TLC27M2CD
TLC274MJ	TLC27L2BIP	TLC27L7CD	TLC27M2CP
TLC274MN	TLC27L2CD	TLC27L7CP	TLC27M2ID
TLC277CD	TLC27L2CP	TLC27L7ID	TLC27M2IP
TLC277CP	TLC27L2ID	TLC27L7IP	TLC27M2MD
TLC277ID	TLC27L2IP	TLC27L7MD	TLC27M2MFK
TLC277IP	TLC27L2MD	TLC27L7MFK	TLC27M2MJG

# Multisim 14.0 Education Components

---

TLC27M2MP	TLC27M9CD	TLC354ID	TLC372MFK
TLC27M4ACD	TLC27M9CN	TLC354IN	TLC372MJG
TLC27M4ACN	TLC27M9ID	TLC354MD	TLC372MP
TLC27M4AID	TLC27M9IN	TLC354MN	TLC372QD
TLC27M4AIN	TLC27M9MD	TLC3702CD	TLC372QP
TLC27M4BCD	TLC27M9MFK	TLC3702CP	TLC374CD
TLC27M4BCN	TLC27M9MJ	TLC3702ID	TLC374CN
TLC27M4BID	TLC27M9MN	TLC3702IP	TLC374CPW
TLC27M4BIN	TLC339CD	TLC3702MFK	TLC374ID
TLC27M4CD	TLC339CN	TLC3702MJG	TLC374IN
TLC27M4CN	TLC339ID	TLC3702QJG	TLC374MD
TLC27M4ID	TLC339IN	TLC3704CD	TLC374MFK
TLC27M4IN	TLC339MD	TLC3704CN	TLC374MJ
TLC27M4MD	TLC339MN	TLC3704CPW	TLC374MN
TLC27M4MFK	TLC339QD	TLC3704ID	TLC374QD
TLC27M4MJ	TLC339QN	TLC3704IN	TLC374QN
TLC27M4MN	TLC352CD	TLC3704MFK	TLC393CD
TLC27M7CD	TLC352CP	TLC3704MJ	TLC393CP
TLC27M7CP	TLC352ID	TLC3704QJ	TLC393ID
TLC27M7ID	TLC352IP	TLC372CD	TLC393IP
TLC27M7IP	TLC352MFK	TLC372CP	TLC393MD
TLC27M7MD	TLC352MJG	TLC372CPW	TLC393MFK
TLC27M7MFK	TLC354CD	TLC372ID	TLC393MJG
TLC27M7MJG	TLC354CN	TLC372IP	TLC393MP
TLC27M7MP	TLC354CPW	TLC372MD	TLC551CD

# Multisim 14.0 Education Components

---

TLC551CP	TLE2021CD	TLE2022Y	TLE2027ACD
TLC552C	TLE2021CDBLE	TLE2024ACDW	TLE2027ACP
TLC552CD	TLE2021CP	TLE2024ACN	TLE2027AID
TLC552CN	TLE2021CPWLE	TLE2024AIDW	TLE2027AIP
TLC555CD	TLE2021ID	TLE2024AIN	TLE2027AMD
TLC555CP	TLE2021IP	TLE2024AMDW	TLE2027AMFK
TLC555CPSR	TLE2021MD	TLE2024AMFK	TLE2027AMJG
TLC555CPW	TLE2021MFK	TLE2024AMJ	TLE2027AML
TLC555ID	TLE2021MJG	TLE2024AMN	TLE2027AMP
TLC555IP	TLE2021MP	TLE2024BCDW	TLE2027CD
TLC555QDR	TLE2021Y	TLE2024BCN	TLE2027CP
TLC556CD	TLE2022ACD	TLE2024BIDW	TLE2027ID
TLC556CN	TLE2022ACP	TLE2024BIN	TLE2027IP
TLC556ID	TLE2022AID	TLE2024BMDW	TLE2027MD
TLC556IN	TLE2022AIP	TLE2024BMJ	TLE2027MFK
TLE2021ACD	TLE2022BCD	TLE2024BMN	TLE2027MJG
TLE2021ACP	TLE2022BCP	TLE2024CDW	TLE2027ML
TLE2021AID	TLE2022BID	TLE2024CN	TLE2027MP
TLE2021AIP	TLE2022BIP	TLE2024IDW	TLE2037ACD
TLE2021AMD	TLE2022CD	TLE2024IN	TLE2037ACP
TLE2021AMFK	TLE2022CDBLE	TLE2024MDW	TLE2037AID
TLE2021AMJG	TLE2022CP	TLE2024MFK	TLE2037AIP
TLE2021AMP	TLE2022CPWLE	TLE2024MJ	TLE2037AMD
TLE2021BI	TLE2022ID	TLE2024MN	TLE2037AMFK
TLE2021BMJG	TLE2022IP	TLE2024Y	TLE2037AMJG

# Multisim 14.0 Education Components

---

TLE2037AML	TLE2061BMJG	TLE2062BCD	TLE2064BCN
TLE2037AMP	TLE2061BML	TLE2062BCP	TLE2064BIN
TLE2037CD	TLE2061BMP	TLE2062BID	TLE2064BMJ
TLE2037CP	TLE2061CD	TLE2062BIP	TLE2064BMN
TLE2037ID	TLE2061CDBLE	TLE2062BMD	TLE2064CD
TLE2037IP	TLE2061CL	TLE2062BMFK	TLE2064CN
TLE2037MD	TLE2061CP	TLE2062BMJG	TLE2064ID
TLE2037MFK	TLE2061CPWLE	TLE2062BMP	TLE2064IN
TLE2037MJG	TLE2061ID	TLE2062CD	TLE2064MD
TLE2037ML	TLE2061IL	TLE2062CP	TLE2064MFK
TLE2037MP	TLE2061IP	TLE2062ID	TLE2064MJ
TLE2061ACD	TLE2061MD	TLE2062IP	TLE2064MN
TLE2061ACL	TLE2061MFK	TLE2062MD	TLE2064Y
TLE2061ACP	TLE2061MJG	TLE2062MFK	TLE2071CD
TLE2061AID	TLE2061ML	TLE2062MJG	TLE2071CP
TLE2061AIL	TLE2061MP	TLE2062MP	TLE2071MFK
TLE2061AIP	TLE2061Y	TLE2062Y	TLE2071MJG
TLE2061AMD	TLE2062ACD	TLE2064ACD	TLE2072CD
TLE2061AMFK	TLE2062ACP	TLE2064ACN	TLE2072CP
TLE2061AMJG	TLE2062AID	TLE2064AID	TLE2072MFK
TLE2061AML	TLE2062AIP	TLE2064AIN	TLE2074CN
TLE2061AMP	TLE2062AMD	TLE2064AMD	TLE2081CD
TLE2061BCL	TLE2062AMFK	TLE2064AMFK	TLE2081CP
TLE2061BIL	TLE2062AMJG	TLE2064AMJ	TLE2081MFK
TLE2061BIP	TLE2062AMP	TLE2064AMN	TLE2081MJG

# Multisim 14.0 Education Components

---

TLE2082ACD	TLE2141CD	TLE2142Y	TLE2161BIP
TLE2082ACP	TLE2141CP	TLE2144ACN	TLE2161BMJ
TLE2082AID	TLE2141ID	TLE2144AIN	TLE2161BML
TLE2082AIP	TLE2141IP	TLE2144AMFK	TLE2161BMP
TLE2082AMD	TLE2141MD	TLE2144AMJ	TLE2161CD
TLE2082AMFK	TLE2141MFK	TLE2144AMN	TLE2161CP
TLE2082AMJG	TLE2141MJG	TLE2144CDW	TLE2161ID
TLE2082AMP	TLE2141MP	TLE2144CN	TLE2161IP
TLE2082CD	TLE2141Y	TLE2144IDW	TLE2161MD
TLE2082CP	TLE2142ACD	TLE2144IN	TLE2161MFK
TLE2082ID	TLE2142ACP	TLE2144MDW	TLE2161MJG
TLE2082IP	TLE2142AID	TLE2144MFK	TLE2161ML
TLE2082MD	TLE2142AIP	TLE2144MJ	TLE2161MP
TLE2082MFK	TLE2142AMD	TLE2144MN	TLE2227ACP
TLE2082MJG	TLE2142AMFK	TLE2144Y	TLE2227CDW
TLE2082MP	TLE2142AMJG	TLE2161ACD	TLE2227CP
TLE2084CN	TLE2142AMP	TLE2161ACP	TLE2237ACP
TLE2141ACD	TLE2142CD	TLE2161AID	TLE2237CDW
TLE2141ACP	TLE2142CP	TLE2161AIP	TLE2237CP
TLE2141AID	TLE2142ID	TLE2161AMD	TLE2425CD
TLE2141AIP	TLE2142IP	TLE2161AMFK	TLE2425ID
TLE2141AMD	TLE2142MD	TLE2161AMJG	TLE2426CD
TLE2141AMFK	TLE2142MFK	TLE2161AML	TLE2426IP
TLE2141AMJG	TLE2142MJG	TLE2161AMP	TL-OP
TLE2141AMP	TLE2142MP	TLE2161BCP	TL-OP1



# Multisim 14.0 Education Components

---

TLV2211CDBV	TLV2264AIPWLE	TLV2344IPWLE	TLV2373IDGS
TLV2211IDBV	TLV2264ID	TLV2352ID	TLV2373IN
TLV2221CDBV	TLV2264IN	TLV2352IP	TLV2374ID
TLV2221IDBV	TLV2264MJ	TLV2352IPW	TLV2374IN
TLV2231CDBV	TLV2264QD	TLV2354ID	TLV2374IPW
TLV2231IDBV	TLV2322ID	TLV2354IN	TLV2375ID
TLV2252ID	TLV2322IP	TLV2354IPW	TLV2375IN
TLV2252IP	TLV2322IPWLE	TLV2354MJ	TLV2375IPW
TLV2252MFK	TLV2324ID	TLV2361CDBV	TLV2401CD
TLV2252MJG	TLV2324IN	TLV2361IDBV	TLV2401CDBV
TLV2252MU	TLV2324IPWLE	TLV2362ID	TLV2401ID
TLV2254AID	TLV2332ID	TLV2362IDGK	TLV2401IDBV
TLV2254AIN	TLV2332IP	TLV2362IP	TLV2401IP
TLV2254AIPWLE	TLV2332IPWLE	TLV2362IPS	TLV2402CD
TLV2254ID	TLV2334ID	TLV2362IPW	TLV2402CDGK
TLV2254IN	TLV2334IN	TLV2370ID	TLV2402ID
TLV2254MFK	TLV2334IPWLE	TLV2370IDBV	TLV2402IDGK
TLV2254MJ	TLV2341ID	TLV2370IP	TLV2402IP
TLV2254QD	TLV2341IP	TLV2371ID	TLV2432AID
TLV2262AIPWLE	TLV2341IPWLE	TLV2371IDBV	TLV2432AIPW
TLV2262ID	TLV2342ID	TLV2371IP	TLV2432AMJG
TLV2262IP	TLV2342IP	TLV2372ID	TLV2434AID
TLV2262MFK	TLV2342IPWLE	TLV2372IDGK	TLV2434AIPW
TLV2262MJG	TLV2344ID	TLV2372IP	TLV2442CD
TLV2262MU	TLV2344IN	TLV2373ID	TLV2442CPW

# Multisim 14.0 Education Components

---

TLV2442MJG	TLV2470AID	TLV274CPW	TLV2782AID
TLV2444CD	TLV2470AIP	TLV274ID	TLV2783AID
TLV2444CPW	TLV2471AID	TLV274IN	TLV2784AID
TLV2444ID	TLV2471AIP	TLV274IPW	TLV2784AIPW
TLV2444IPW	TLV2472AID	TLV2760ID	TLV2785AID
TLV2450AID	TLV2472AIP	TLV2760IDBV	TLV2785AIPW
TLV2450AIP	TLV2473AID	TLV2760IP	TLV3012AIDBVR
TLV2451AID	TLV2473AIP	TLV2761ID	TLV3012AIDCKR
TLV2451AIP	TLV2474AID	TLV2761IDBV	TLV3201AIDBVR
TLV2452AID	TLV2474AIN	TLV2761IP	TLV3201AIDCKR
TLV2452AIP	TLV2474AIPWP	TLV2762ID	TLV3202AID
TLV2453AID	TLV2475AID	TLV2762IDGK	TLV3202AIDGK
TLV2453AIN	TLV2475AIN	TLV2762IP	TLV3401CD
TLV2454AID	TLV2475AIPWP	TLV2763ID	TLV3401CDBVR
TLV2454AIN	TLV271CD	TLV2763IDGS	TLV3401ID
TLV2454AIPW	TLV271CDBVR	TLV2763IN	TLV3401IDBVR
TLV2455AID	TLV271ID	TLV2764ID	TLV3401IDG4
TLV2455AIN	TLV271IDBVR	TLV2764IN	TLV3401IP
TLV2455AIPW	TLV271IP	TLV2764IPW	TLV342ID
TLV2460CD	TLV272CD	TLV2765ID	TLV342IDGKR
TLV2460CDBV	TLV272CDGK	TLV2765IN	TLV342IRUGR
TLV2460CP	TLV272ID	TLV2765IPW	TLV3501AID
TLV2461CD	TLV272IDGK	TLV2772CD	TLV3501AIDBVR
TLV2461CDBV	TLV272IP	TLV2772CDGK	TLV3691IDCKR
TLV2461CP	TLV274CD	TLV2772CP	TLV3691IDPFR

# Multisim 14.0 Education Components

---

TLV3701CD	TLV431CLPM	TMP20AIDCKR	TPSMB39A-E3/2T
TLV3701CDBVR	TLV431CLPR	TMP20AIDRLR	TPSMC22A-E3/57T
TLV3701ID	TLV431IDBVR	TN2219	TPSMC27A-E3/57T
TLV3701IDBVR	TLV431IDBZR	TN2219A	TPSMC30AHE3_A/H
TLV3701IP	TLV431ILP	TN2905	TPSMC33A-E3/51T
TLV4110ID	TLV431ILPR	TN2905A	TPSMC36A/9AT
TLV4110IDGNR	TLV431QPK	TN4036	TPSMC39A-E3/57T
TLV4110IP	TLVH431CDBVR	TOSHIBA-MIPS-HDR	TPSMP18AHM3/84 A
TLV4111CD	TLVH431CDBZR	TPA301D	TPSMP24AHM3/84 A
TLV4111CDGN	TLVH431CDCKR	TPA301DGN	TPSMP27AHE3/84A
TLV4111ID	TLVH431CLP	TPA301DR	TPSMP30AHM3/84 A
TLV4111IDGN	TLVH431CLPR	TPS76150DBVR	TPSMP36AHM3/84 A
TLV4112CD	TLVH431CPK	TPS780230300DRV R	TPSMA16AHE3/61T
TLV4112CDGN	TLVH431IDBVR	TPSMA20A/11T	TRAFFIC_LIGHT
TLV4112CP	TLVH431IDBZR	TPSMA27AHE3/61T	TRAFFIC_LIGHT_SIN GLE
TLV4112ID	TLVH431IDCKR	TPSMA30AHE3/61T	TRANSFER_FUNCTI ON_BLOCK
TLV4112IDGN	TLVH431ILP	TPSMA33AHE3/61T	TRANSFORMER_CT _RATED
TLV4112IP	TLVH431ILPR	TPSMA36AHE3/5AT	TRANSFORMER_RA TED
TLV4113CDGQR	TLVH431IPK	TPSMB24AHE3/52T	TRANSISTOR
TLV4113ID	TLVH431QDBVR	TPSMB27A/2	TRANSISTOR_DELA Y
TLV4113IDGQ	TLVH431QDBZR	TPSMB30AHE3/52T	
TLV4113IN	TLVH431QDCKR	TPSMB33AHE3/52T	
TLV431CDBVR	TLVH431QLP	TPSMB36A/5T	
TLV431CDBZR	TLVH431QLPR		
TLV431CLP	TLVH431QPK		

# Multisim 14.0 Education Components

---

TRANSISTOR_DIODE	U406	UA747CN	US1M-E3/61T
	U440	UA747MFK	UVLO
TRANSISTOR_DIODE_DELAY	U441	UA747MJ	UX60-MB-5ST
TRANSPORT_DELAY	UA709AMJ	UA747MW	V_REF1
TRF37A75IDSGR	UA709AMJG	UA748CD	V_REF2
TRF37B75IDSGR	UA709AMU	UA748CP	V_REF3
TRF37C75IDSGR	UA709AMW	UA748JG	V_REF4
TRIAC	UA709CD	UA748MJG	V_REF5
TRIANGULAR_CURRENT	UA709CJG	UA748MU	V10P10-M3/86A
	UA709CP	UC1705	V12P10-M3/86A
TRIANGULAR_VOLTAGE	UA709MJ	UC3248	V8P10HM3/86A
TRIODE_VIRTUAL	UA709MU	UC3842	VARIABLE_CAPACITOR
TRISTATE	UA709MW	UF4002-E3/54	VARIABLE_CAPACITOR_RATED
TRISTATE_NEG	UA723CD	UF4007-E3/54	VARIABLE_CAPACITOR_VIRTUAL
TS_VIRTUAL	UA723CFK	UF5406-E3/54	
U257	UA723CJ	UG06D-E3/54	
U308	UA723CN	UG1D-E3/54	VARIABLE_INDUCTOR
U309	UA723MU	UG30DPT-E3/45	VARIABLE_INDUCTOR_RATED
U310	UA741CD	UG5JT-E3/45	VARIABLE_INDUCTOR_VIRTUAL
U401	UA741CP	UG8DT-E3/45	VARIABLE_PULLUP_VIRTUAL
U402	UA741MFK	UG8JCT-E3/45	
U403	UA741MJ	UG8JT-E3/45	
U404	UA741MJG	UNDCD_BARGRAPH	VARIABLE_RESISTOR_VIRTUAL
U405	UA741MU	US1G-E3/61T	
	UA747CD	US1J-E3/5AT	VARICAP

# Multisim 14.0 Education Components

---

VARICOIL	VO0631-X001T	VO615A-3X007T	VOLTAGE_CONTROLLED_SPST
VARIRES	VO0661T	VO615A-3X008T	
VBP104FAS	VO2601	VO615A-3X009T	VOLTAGE_CONTROLLED_SPST_ANIMATED
VBP104FASR	VO2601-X006	VO615A-3X016	
VBPW34FAS	VO2601-X007T	VO615A-3X017T	VOLTAGE_CONTROLLED_SPST_BOUNCE
VBPW34FASR	VO2601-X016	VO615A-3X018T	
VBPW34S	VO2601-X017T	VO615A-3X019T	VOLTAGE_CONTROLLED_SQUARE_WAVE
VBPW34SR	VO2611	VOLTAGE_CONTROLLED_CAPACITOR_VIRTUAL	
VCA810AID	VO2611-X006		VOLTAGE_CONTROLLED_TRIANGLE_WAVE
VCA810ID	VO2611-X007T	VOLTAGE_CONTROLLED_CURRENT_SOURCE	
VCA821ID	VO2611-X016		VOLTAGE_CONTROLLED_VOLTAGE_SOURCE
VCA824ID	VO2611-X017T	VOLTAGE_CONTROLLED_DPDT	
VCA8500IRGCR	VO2630		VOLTAGE_DIFFERENTIATOR
VCC	VO2630-X006	VOLTAGE_CONTROLLED_INDUCTOR_VIRTUAL	
VDAC	VO2630-X007T		VOLTAGE_GAIN_BLOCK
VDAC16	VO2631	VOLTAGE_CONTROLLED_LIMITER	
VDD	VO2631-X006		VOLTAGE_HYSTEREISIS_BLOCK
VEE	VO2631-X007T	VOLTAGE_CONTROLLED_PIECEWISE_LINEAR_SOURCE	
VN10LF	VO2631-X017T		VOLTAGE_INTEGRATOR
VO0600T	VO4661	VOLTAGE_CONTROLLED_RESISTOR_VIRTUAL	VOLTAGE_LIMITER
VO0601T	VO4661-X006		VOLTAGE_SLEWRATE_BLOCK
VO0601-X001T	VO4661-X007T	VOLTAGE_CONTROLLED_SINE_WAVE	
VO0611T	VO615A-3		VOLTAGE_SUMMER
VO0630T	VO615A-3X001	VOLTAGE_CONTROLLED_SPDT	VOLTAGE_TRIGGERED_PIECEWISE_LINEAR_SOURCE
VO0631T	VO615A-3X006		

# Multisim 14.0 Education Components

---

VOLTMETER_H	XNOR7	Z4KE100	ZC823
VOLTMETER_HR	XNOR8	Z4KE100A	ZC824
VOLTMETER_V	XNOR8	Z4KE110	ZC825
VOLTMETER_VR	XOR2	Z4KE110A	ZC826
VOM452T	XOR2	Z4KE120	ZC830A
VOM453T	XOR3	Z4KE120A	ZC831A
VSS	XOR3	Z4KE130	ZC832A
VTERM	XOR4	Z4KE130A	ZC833A
W06G-E4/51	XOR4	Z4KE140	ZC834A
WE300B	XOR5	Z4KE140A	ZC835A
WOBBLE_STICK	XOR5	Z4KE150	ZC836A
XILINX-PARALLEL- III-IV-HDR	XOR6	Z4KE150A	ZDX1F
	XOR6	Z4KE160	ZDX2F
XILINX-PARALLEL- IV-HDR	XOR7	Z4KE160A	ZDX5
	XOR7	Z4KE170	ZENER
XNOR2	XOR8	Z4KE170A	ZGL41_100
XNOR2	XOR8	Z4KE180	ZGL41_110
XNOR3	XTR300AIRGWR	Z4KE180A	ZGL41_120
XNOR4	Z_LOAD1	Z4KE190	ZGL41_130
XNOR4	Z_LOAD1_DELTA	Z4KE190A	ZGL41_140
XNOR5	Z_LOAD1_WYE	Z4KE200	ZGL41_150
XNOR5	Z_LOAD2	Z4KE200A	ZGL41_160
XNOR6	Z_LOAD2_DELTA	ZC820	ZGL41_170
XNOR6	Z_LOAD2_WYE	ZC821	ZGL41_180
XNOR7	Z_LOAD3	ZC822	ZGL41_190

# Multisim 14.0 Education Components

---

ZGL41_200	ZPD6.8	ZTX237B	ZTX650
ZHCS1000	ZPD7.5	ZTX238	ZTX651
ZHCS750	ZPD8.2	ZTX238B	ZTX653
ZPD10	ZTX1047A	ZTX239	ZTX657
ZPD11	ZTX1048A	ZTX239B	ZTX658
ZPD12	ZTX1049A	ZTX320	ZTX688B
ZPD13	ZTX1051A	ZTX321	ZTX689B
ZPD15	ZTX1053A	ZTX325	ZTX690B
ZPD16	ZTX1055A	ZTX327	ZTX692B
ZPD18	ZTX107	ZTX337A	ZTX694B
ZPD2.7	ZTX107B	ZTX338A	ZTX696B
ZPD20	ZTX108	ZTX360	ZTX704
ZPD22	ZTX108B	ZTX450	ZTX705
ZPD24	ZTX109	ZTX454	ZTX718
ZPD27	ZTX109B	ZTX455	ZTX749
ZPD3.0	ZTX1147A	ZTX458	ZTX750
ZPD3.3	ZTX1149A	ZTX549	ZTX751
ZPD3.6	ZTX1151A	ZTX550	ZTX753
ZPD3.9	ZTX212	ZTX558	ZTX757
ZPD30	ZTX212A	ZTX601B	ZTX758
ZPD33	ZTX213	ZTX604	ZTX788A
ZPD4.3	ZTX213A	ZTX605	ZTX788B
ZPD4.7	ZTX214	ZTX614	ZTX789A
ZPD5.1	ZTX214A	ZTX618	ZTX790A
ZPD6.2	ZTX237	ZTX649	ZTX792A

# Multisim 14.0 Education Components

---

ZTX795A	ZVP2106A
ZTX796A	ZVP2106G
ZTX849	ZVP3306
ZTX851	ZVP3306F
ZTX857	ZVP4424A
ZTX869	ZVP4424G
ZTX948	
ZTX949	
ZTX951	
ZTX953	
ZTX955	
ZTX956	
ZTX957	
ZTX958	
ZTX968	
ZVN0124A	
ZVN2106A	
ZVN2106G	
ZVN3306A	
ZVN3306F	
ZVN3310F	
ZVN4210G	
ZVN4306G	
ZVN4310G	
ZVN4424G	