

Multisim 14.0 Full Components

741	1787386	1 mF [T510X108M004AT	1 mF [T520Y108M2R5AT
1028	1787580	E018]	E015]
1294	685119136923	1 mF	1 mF
2462	0.5_AMP	[T510X108M004AT	[T520Y108M2R5AT
2466	02BZ2.2	E023]	E025]
2468	02DZ4.7	1 mF	1 mF
2477	05AZ2.2	[T513E108M004AH	[T530X108M003AT
2481	1 mF	6110]	E010]
8051	[T491E108M004AT]	1 mF	1 mF
8052	1 mF	[T513X108M004AH	[T530X108M004AT
284258	[T491X108M004AT]	6110]	E006]
1708026	1 mF	1 mF	1 mF
1708039	[T494E108M004AT]	[T513X108M004AH	[T530X108M2R5AT
1708042	1 mF	6120]	E005]
1708055	[T494X108M004AT]	1 mF	1 mF
1708084	1 mF	[T520D108M2R5AT	[T530X108M2R5AT
1708110	[T495E108M004AT	E015]	E006]
1786837	E035]	1 mF	1 mF
1786866	1 mF	[T520D108M2R5AT	[T530Y108M2R5AT
1786918	[T495X108M004AT	E030]	E005]
1786963	E070]	1 mF	1 nF
1787205	1 mF	[T520X108M003AT	[C0402C102K1HACT
1787234	[T495E108M006AT	E015]	U]
1787289	E050]	1 mF	1 nF
1787331	1 mF	[T520X108M003AT	[C0402C102K3GACT
	[T495X108M004AT	E030]	U]
	E010]	1 mF	1 nF
	[T510E108M004AT	[T520X108M2R5AT	[C0402C102K3HACT
	E010]	E010]	U]
	1 mF	1 mF	1 nF
	[T510E108M004AT	[T520Y108M2R5AT	[C0402C102K3RACT
	E018]	E010]	U]

Multisim 14.0 Full Components

1 nF [C0402C102K4RACT U]	1 nF [C0603C102K4GACT U]	1 nF [C0805C102K3RACT U]	1 nF [C1206C102K4RACT U]
1 nF [C0402C102K5HACT U]	1 nF [C0603C102K4RACT U]	1 nF [C0805C102K4RACT U]	1 nF [C1206C102K5GACT U]
1 nF [C0402C102K5RACT U]	1 nF [C0603C102K5GACT U]	1 nF [C0805C102K5GACT U]	1 nF [C1206C102K5RACT U]
1 nF [C0402C102K8RACT U]	1 nF [C0603C102K5HACT U]	1 nF [C0805C102K5RACT U]	1 nF [C1206C102KCGAC TU]
1 nF [C0402C102K9RACT U]	1 nF [C0603C102K5RACT U]	1 nF [C0805C102K8RACT U]	1 nF [C1210C102K1GACT U]
1 nF [C0603C102K1HACT U]	1 nF [C0603C102K8RACT U]	1 nF [C0805C102KARACT U]	1 nF [C1210C102K2GACT U]
1 nF [C0603C102K1RACT U]	1 nF [C0603C102K9RACT U]	1 nF [C1206C102K1GACT U]	1 nF [C1210C102K5GACT U]
1 nF [C0603C102K2RACT U]	1 nF [C0805C102K1GACT U]	1 nF [C1206C102K1RACT U]	1 nF [C1210C102KBGAC TU]
1 nF [C0603C102K3GACT U]	1 nF [C0805C102K1RACT U]	1 nF [C1206C102K2GACT U]	1 nF [C1210C102KCGAC TU]
1 nF [C0603C102K3HACT U]	1 nF [C0805C102K2RACT U]	1 nF [C1206C102K2RACT U]	1 nF [C1210C102KDGAC TU]
1 nF [C0603C102K3RACT U]	1 nF [C0805C102K3GACT U]	1 nF [C1206C102K3RACT U]	1 nF [C1812C102K1GACT U]

Multisim 14.0 Full Components

1 nF [C1812C102K2GACT U]	1 nF [CA064C102K8RACT U]	1 uF [C0805C105K4PACT U]	1 uF [C1206C105K3PACT U]
1 nF [C1812C102K5GACT U]	1 uF [C0402C105K8PACT U]	1 uF [C0805C105K4RACT U]	1 uF [C1206C105K3RACT U]
1 nF [C1812C102KBGAC TU]	1 uF [C0402C105K9PACT U]	1 uF [C0805C105K8NAC TU]	1 uF [C1206C105K4RACT U]
1 nF [C1812C102KCGAC TU]	1 uF [C0603C105K3PACT U]	1 uF [C0805C105K8PACT U]	1 uF [C1206C105K5RACT U]
1 nF [C1812C102KDGAC TU]	1 uF [C0603C105K4PACT U]	1 uF [C0805C105K8RACT U]	1 uF [C1206C105K8RACT U]
1 nF [C1825C102KBGAC TU]	1 uF [C0603C105K4RACT U]	1 uF [C0805C105K9PACT U]	1 uF [C1206C105K9RACT U]
1 nF [C2220C102KBGAC TU]	1 uF [C0603C105K8PACT U]	1 uF [C0805C105K9RACT U]	1 uF [C1206C105M3VAC TU]
1 nF [C2225C102KBGAC TU]	1 uF [C0603C105K8RACT U]	1 uF [C0805C105M3VAC TU]	1 uF [C1206C105M4VAC TU]
1 nF [CA064C102K3RACT U]	1 uF [C0603C105K9PACT U]	1 uF [C0805C105M4VAC TU]	1 uF [C1206C105M8VAC TU]
1 nF [CA064C102K4RACT U]	1 uF [C0603C105K9RACT U]	1 uF [C0805C105M8VAC TU]	1 uF [C1206F105K4RACT U]
1 nF [CA064C102K5RACT U]	1 uF [C0805C105K3PACT U]	1 uF [C1206C105K3NAC TU]	1 uF [C1210C105K1RACT U]

Multisim 14.0 Full Components

1 uF [C1210C105K3PACT U]	1 uF [C1210C105M8VAC TU]	1 uF [C1825C105KARACT U]	1 uF [T491A105M016AT]
1 uF [C1210C105K3RACT U]	1 uF [C1210F105K3RACT U]	1 uF [C1825C105M5UAC TU]	1 uF [T491A105M020AT]
1 uF [C1210C105K4PACT U]	1 uF [C1210F105K4RACT U]	1 uF [C2220C105K5R1C7 186]	1 uF [T491A105M025AT]
1 uF [C1210C105K4RACT U]	1 uF [C1812C105K3RACT U]	1 uF [C2220C105K5RACT U]	1 uF [T491B105M025AT]
1 uF [C1210C105K5NAC TU]	1 uF [C1812C105K5RACT U]	1 uF [C2220C105KARACT U]	1 uF [T491B105M035AT]
1 uF [C1210C105K5PACT U]	1 uF [C1812C105M5UAC TU]	1 uF [C2225C105K1RACT U]	1 uF [T491B105M050AT]
1 uF [C1210C105K5RACT U]	1 uF [C1812F105K1RACT U]	1 uF [C2225C105K5RACT U]	1 uF [T491C105M050AT]
1 uF [C1210C105K8RACT U]	1 uF [C1812F105K3RACT U]	1 uF [C2225C105KARACT U]	1 uF [T491S105M020AT]
1 uF [C1210C105K9RACT U]	1 uF [C1812F105K5RACT U]	1 uF [C2225C105M5UAC TU]	1 uF [T491V105M050AT]
1 uF [C1210C105M3VAC TU]	1 uF [C1825C105K2RACT U]	1 uF [T409C105M025AH 4250]	1 uF [T494A105M016AT]
1 uF [C1210C105M5UAC TU]	1 uF [C1825C105K5RACT U]	1 uF [T489A105M025AT E6K6]	1 uF [T494A105M020AT]
			1 uF [T494A105M025AT]
			1 uF [T494A105M035AT]
			1 uF [T494B105M025AT]

Multisim 14.0 Full Components

1 uF [T494B105M035AT]	1.1 nF [C0402C112K3HACT U]	1.2 nF [C0402C122K3HACT U]	1.2 nF [C0603C122K5RACT U]
1 uF [T494B105M050AT]	1.1 nF [C0402C112K5HACT U]	1.2 nF [C0402C122K3RACT U]	1.2 nF [C0805C122K1GACT U]
1 uF [T494C105M050AT]	1.1 nF [C0603C112K1HACT U]	1.2 nF [C0402C122K4RACT U]	1.2 nF [C0805C122K1RACT U]
1 uF [T494V105M050AT]	1.1 nF [C0603C112K3HACT U]	1.2 nF [C0402C122K5HACT U]	1.2 nF [C0805C122K2RACT U]
1 uF [T495A105M020AT E3K0]	1.1 nF [C0603C112K5HACT U]	1.2 nF [C0402C122K5RACT U]	1.2 nF [C0805C122K3GACT U]
1 uF [T495A105M035AT E3K0]	1.1 nF [C1210C112KBGAC TU]	1.2 nF [C0603C122K1HACT U]	1.2 nF [C0805C122K4RACT U]
1 uF [T495B105M035AT E1K7]	1.1 nF [C1812C112KBGAC TU]	1.2 nF [C0603C122K1RACT U]	1.2 nF [C0805C122K5GACT U]
1 uF [T497A105M015AT 6110]	1.1 nF [C1825C112KBGAC TU]	1.2 nF [C0603C122K3HACT U]	1.2 nF [C0805C122K5RACT U]
1 uF [T498A105M016AT E6K5]	1.1 nF [C2220C112KBGAC TU]	1.2 nF [C0603C122K3RACT U]	1.2 nF [C0805C122KARACT U]
1 uF [T498A105M020AT E5K9]	1.1 nF [C2225C112KBGAC TU]	1.2 nF [C0603C122K4RACT U]	1.2 nF [C1206C122K1GACT U]
1 uF [T498A105M035AT E10K]	1.1 nF [CDR33BP112BKSM]	1.2 nF [C0603C122K5HACT U]	1.2 nF [C1206C122K1RACT U]

Multisim 14.0 Full Components

1.2 nF [C1206C122K2GACT U]	1.2 uF [C0805C125K8PACT U]	1.2 uF [C1825C125M5UAC TU]	1.3 nF [C2220C132KBGAC TU]
1.2 nF [C1206C122K2RACT U]	1.2 uF [C0805C125K8RACT U]	1.2 uF [C2220C125K5RACT U]	1.3 nF [C2225C132KBGAC TU]
1.2 nF [C1206C122K5GACT U]	1.2 uF [C0805C125K9PACT U]	1.2 uF [C2225C125KARACT U]	1.5 mF [T530X158M003AT E008]
1.2 nF [C1206C122K5RACT U]	1.2 uF [C0805C125K9RACT U]	1.3 nF [C0402C132K3HACT U]	1.5 mF [T530X158M2R5AT E005]
1.2 nF [C1210C122KBGAC TU]	1.2 uF [C1206C125K3RACT U]	1.3 nF [C0402C132K5HACT U]	1.5 nF [C0402C152K3HACT U]
1.2 nF [C1812C122KBGAC TU]	1.2 uF [C1206C125K4RACT U]	1.3 nF [C0603C132K1HACT U]	1.5 nF [C0402C152K3RACT U]
1.2 nF [C1825C122KBGAC TU]	1.2 uF [C1206C125K8RACT U]	1.3 nF [C0603C132K3HACT U]	1.5 nF [C0402C152K4RACT U]
1.2 nF [C2220C122KBGAC TU]	1.2 uF [C1210C125K3PACT U]	1.3 nF [C0603C132K5HACT U]	1.5 nF [C0402C152K5HACT U]
1.2 nF [C2225C122KBGAC TU]	1.2 uF [C1210C125K3RACT U]	1.3 nF [C1210C132KBGAC TU]	1.5 nF [C0402C152K5RACT U]
1.2 uF [C0805C125K4PACT U]	1.2 uF [C1210F125K4RACT U]	1.3 nF [C1812C132KBGAC TU]	1.5 nF [C0402C152K8RACT U]
1.2 uF [C0805C125K4RACT U]	1.2 uF [C1825C125K5RACT U]	1.3 nF [C1825C132KBGAC TU]	1.5 nF [C0603C152K1HACT U]

Multisim 14.0 Full Components

1.5 nF [C0603C152K1RACT U]	1.5 nF [C0805C152K3RACT U]	1.5 nF [C1206C152K5RACT U]	1.5 uF [C0805C155K4RACT U]
1.5 nF [C0603C152K2RACT U]	1.5 nF [C0805C152K4GACT U]	1.5 nF [C1210C152K1GACT U]	1.5 uF [C0805C155K8PACT U]
1.5 nF [C0603C152K3HACT U]	1.5 nF [C0805C152K4RACT U]	1.5 nF [C1210C152K5GACT U]	1.5 uF [C0805C155K8RACT U]
1.5 nF [C0603C152K3RACT U]	1.5 nF [C0805C152K5GACT U]	1.5 nF [C1210C152KBGAC TU]	1.5 uF [C0805C155K9PACT U]
1.5 nF [C0603C152K4RACT U]	1.5 nF [C0805C152K5RACT U]	1.5 nF [C1812C152K2GACT U]	1.5 uF [C0805C155K9RACT U]
1.5 nF [C0603C152K5HACT U]	1.5 nF [C0805C152KARACT U]	1.5 nF [C1812C152KBGAC TU]	1.5 uF [C1206C155K3RACT U]
1.5 nF [C0603C152K5RACT U]	1.5 nF [C1206C152K1GACT U]	1.5 nF [C1825C152KBGAC TU]	1.5 uF [C1206C155K4PACT U]
1.5 nF [C0603C152K8RACT U]	1.5 nF [C1206C152K1RACT U]	1.5 nF [C2220C152KBGAC TU]	1.5 uF [C1206C155K4RACT U]
1.5 nF [C0805C152K1GACT U]	1.5 nF [C1206C152K2GACT U]	1.5 nF [C2225C152KBGAC TU]	1.5 uF [C1206C155K8PACT U]
1.5 nF [C0805C152K1RACT U]	1.5 nF [C1206C152K2RACT U]	1.5 nF [CDR04BP152BKSM]	1.5 uF [C1206C155K8RACT U]
1.5 nF [C0805C152K2RACT U]	1.5 nF [C1206C152K5GACT U]	1.5 uF [C0805C155K4PACT U]	1.5 uF [C1206C155K9RACT U]

Multisim 14.0 Full Components

1.5 uF [C1210C155K3PACT U]	1.5 uF [T491A155M010AT]	1.5 uF [T494C155M035AT]	1.5KE47A-E3/54
1.5 uF [C1210C155K3RACT U]	1.5 uF [T491A155M016AT]	1.5 uF [T494C155M050AT]	1.5KE47AG
1.5 uF [C1210C155K4RACT U]	1.5 uF [T491A155M020AT]	1.5 uF [T494D155M050AT]	1.5KE47ARL4G
1.5 uF [C1210C155K4RACT U]	1.5 uF [T491A155M025AT]	1.5 uF [T494S155M020AT]	1.5KE51CA-E3/54
1.5 uF [C1210F155K4RACT U]	1.5 uF [T491B155M025AT]	1.5 uF [T498C155M035AT E3K3]	1.5KE75ARL4G
1.5 uF [C1825C155K5RACT U]	1.5 uF [T491B155M035AT]	1.5KE100A-E3/54	1.5KE91A-E3/54
1.5 uF [C1825C155M5UAC TU]	1.5 uF [T491C155M035AT]	1.5KE100CA-E3/54	1.5KE91ARL4G
1.5 uF [C2220C155K5RACT U]	1.5 uF [T491C155M050AT]	1.5KE110CA-E3/54	1.5SMC12AT3G
1.5 uF [C2225C155K5RACT U]	1.5 uF [T491D155M050AT]	1.5KE12A-E3/54	1.5SMC13A-E3/57T
1.5 uF [C2225C155K5RACT U]	1.5 uF [T491S155M020AT]	1.5KE12CA-E3/54	1.5SMC15AT3G
1.5 uF [C2225C155M5UAC TU]	1.5 uF [T494A155M010AT]	1.5KE130CA-E3/54	1.5SMC15CA- E3/57T
1.5 uF [T419A155M015AH 4250]	1.5 uF [T494A155M016AT]	1.5KE160CA-E3/54	1.5SMC180A- E3/57T
1.5 uF [T489C155M050AT E1K5]	1.5 uF [T494B155M025AT]	1.5KE180A-E3/54	1.5SMC18AT3G
	1.5 uF [T494B155M035AT]	1.5KE18A-E3/54	1.5SMC18CA- E3/57T
		1.5KE200A-E3/54	1.5SMC20AT3G
		1.5KE200CA-E3/54	1.5SMC24AT3G
		1.5KE20A-E3/51	1.5SMC33AT3G
		1.5KE36A-E3/54	1.5SMC39A-E3/57T
		1.5KE36CA-E3/54	1.5SMC39AT3G
		1.5KE39ARL4G	1.5SMC43AT3G
		1.5KE39CA-E3/54	1.5SMC540A- E3/57T
			1.5SMC6.8A/57T

Multisim 14.0 Full Components

1.5SMC6.8AT3G	1.6 nF [C2220C162KBGAC TU]	1.8 nF [C0805C182K1RACT U]	1.8 nF [C1210C182K1GACT U]
1.5SMC6.8CA- E3/57T	1.6 nF [C2225C162KBGAC TU]	1.8 nF [C0805C182K2RACT U]	1.8 nF [C1210C182K2GACT U]
1.5SMC62AT3G	1.8 nF [C0402C182K3RACT U]	1.8 nF [C0805C182K4RACT U]	1.8 nF [C1210C182K5GACT U]
1.5SMC75CA- E3/57T	1.8 nF [C0402C182K5RACT U]	1.8 nF [C0805C182K5GACT U]	1.8 nF [C1210C182KBGAC TU]
1.5SMC91AT3G	1.8 nF [C0603C182K1HACT U]	1.8 nF [C0805C182K5RACT U]	1.8 nF [C1812C182KBGAC TU]
1.6 nF [C0603C162K1HACT U]	1.8 nF [C0603C182K1HACT U]	1.8 nF [C0805C182K5RACT U]	1.8 nF [C1812C182KBGAC TU]
1.6 nF [C0603C162K3HACT U]	1.8 nF [C0603C182K1RACT U]	1.8 nF [C0805C182KARACT U]	1.8 nF [C1825C182KBGAC TU]
1.6 nF [C0603C162K5HACT U]	1.8 nF [C0603C182K3HACT U]	1.8 nF [C1206C182K1GACT U]	1.8 nF [C2220C182KBGAC TU]
1.6 nF [C0805C162K4GACT U]	1.8 nF [C0603C182K3RACT U]	1.8 nF [C1206C182K1RACT U]	1.8 nF [C2225C182KBGAC TU]
1.6 nF [C1206C162K5GACT U]	1.8 nF [C0603C182K5HACT U]	1.8 nF [C1206C182K2GACT U]	1.8 uF [C0805C185K4PACT U]
1.6 nF [C1210C162KBGAC TU]	1.8 nF [C0603C182K5RACT U]	1.8 nF [C1206C182K5GACT U]	1.8 uF [C0805C185K4RACT U]
1.6 nF [C1812C162KBGAC TU]	1.8 nF [C0805C182K1GACT U]	1.8 nF [C1206C182K5RACT U]	1.8 uF [C0805C185K8PACT U]
1.6 nF [C1825C162KBGAC TU]			

Multisim 14.0 Full Components

1.8 uF [C0805C185K8RACT U]	1.8 uF [C2225C185K5RACT U]	10 nF [C0603C103K2RACT U]	10 nF [C0805C103K3GACT U]
1.8 uF [C0805C185K9PACT U]	1.8 uF [C2225C185M5UAC TU]	10 nF [C0603C103K3GACT U]	10 nF [C0805C103K3HACT U]
1.8 uF [C0805C185K9RACT U]	1 AMP [C0201C103K4PACT U]	10 nF [C0603C103K3HACT U]	10 nF [C0805C103K3RACT U]
1.8 uF [C1206C185K3PACT U]	10 nF [C0201C103K8PACT U]	10 nF [C0603C103K3RACT U]	10 nF [C0805C103K4RACT U]
1.8 uF [C1206C185K4RACT U]	10 nF [C0201C103K9PACT U]	10 nF [C0603C103K4RACT U]	10 nF [C0805C103K5GACT U]
1.8 uF [C1206C185K8RACT U]	10 nF [C0402C103K3RACT U]	10 nF [C0603C103K5RACT U]	10 nF [C0805C103K5HACT U]
1.8 uF [C1210C185K3PACT U]	10 nF [C0402C103K4RACT U]	10 nF [C0603C103K8RACT U]	10 nF [C0805C103K5RACT U]
1.8 uF [C1210C185K3RACT U]	10 nF [C0402C103K5RACT U]	10 nF [C0603C103K9RACT U]	10 nF [C0805C103K8RACT U]
1.8 uF [C1210F185K4RACT U]	10 nF [C0402C103K8RACT U]	10 nF [C0805C103K1GACT U]	10 nF [C0805C103KARACT U]
1.8 uF [C1825C185K5RACT U]	10 nF [C0402C103K9RACT U]	10 nF [C0805C103K1HACT U]	10 nF [C0805C103M1UAC TU]
1.8 uF [C2220C185K5RACT U]	10 nF [C0603C103K1RACT U]	10 nF [C0805C103K1RACT U]	10 nF [C0805C103M5UAC TU]

Multisim 14.0 Full Components

10 nF [C0805F103K1RACT U]	10 nF [C1206C103K4GACT U]	10 nF [C1210C103KARACT U]	10 nF [C2225C103K2GACT U]
10 nF [C0805F103K2RACT U]	10 nF [C1206C103K4RACT U]	10 nF [C1812C103K1GACT U]	10 nF [C2225C103KCGAC TU]
10 nF [C0805F103K3RACT U]	10 nF [C1206C103K5HACT U]	10 nF [C1812C103K1RACT U]	10 nF [CA064C103K3RACT U]
10 nF [C0805F103K4RACT U]	10 nF [C1206C103K5RACT U]	10 nF [C1812C103K2RACT U]	10 nF [CA064C103K4RACT U]
10 nF [C0805F103K5RACT U]	10 nF [C1206C103KARACT U]	10 nF [C1812C103K5GACT U]	10 nF [CA064C103K5RACT U]
10 nF [C1206C103K1HACT U]	10 nF [C1206C103M1UAC TU]	10 nF [C1812C103K5RACT U]	10 nF [CA064C103K8RACT U]
10 nF [C1206C103K1RACT U]	10 nF [C1206C103M5UAC TU]	10 nF [C1825C103K1GACT U]	10 pF [C0402C100K3GACT U]
10 nF [C1206C103K2RACT U]	10 nF [C1210C103K1RACT U]	10 nF [C1825C103K2GACT U]	10 pF [C0402C100K4GACT U]
10 nF [C1206C103K3GACT U]	10 nF [C1210C103K2RACT U]	10 nF [C1825C103K5GACT U]	10 pF [C0402C100K5GACT U]
10 nF [C1206C103K3HACT U]	10 nF [C1210C103K5GACT U]	10 nF [C2220C103K1GACT U]	10 pF [C0402C100K8GACT U]
10 nF [C1206C103K3RACT U]	10 nF [C1210C103K5RACT U]	10 nF [C2220C103K2GACT U]	10 pF [C0603C100K1GACT U]

Multisim 14.0 Full Components

10 pF [C0603C100K2GACT U]	10 pF [C1206C100K5GACT U]	10 pF [CA064C100K4GAC TU]	10 uF [C1206C106K8PACT U]
10 pF [C0603C100K3GACT U]	10 pF [C1206C100KBGAC TU]	10 pF [CA064C100K5GAC TU]	10 uF [C1206C106K8RACT U]
10 pF [C0603C100K5GACT U]	10 pF [C1210C100K2GACT U]	10 uF [A700V106M016AT E045]	10 uF [C1206C106K9PACT U]
10 pF [C0805C100K1GACT U]	10 pF [C1210C100K5GACT U]	10 uF [A700V106M12RAT E060]	10 uF [C1206C106K9RACT U]
10 pF [C0805C100K2GACT U]	10 pF [C1210C100KBGAC TU]	10 uF [C0805C106K4PACT U]	10 uF [C1206C106M8VAC TU]
10 pF [C0805C100K5GACT U]	10 pF [C1812C100KBGAC TU]	10 uF [C0805C106K8PACT U]	10 uF [C1206C106M9VAC TU]
10 pF [C0805C100KBGAC TU]	10 pF [C1825C100KBGAC TU]	10 uF [C0805C106K9PACT U]	10 uF [C1210C106K3PACT U]
10 pF [C0805C100KDGAC TU]	10 pF [C2220C100KBGAC TU]	10 uF [C0805C106M9VAC TU]	10 uF [C1210C106K3RACT U]
10 pF [C0805H100K5GAC TU]	10 pF [C2225C100KBGAC TU]	10 uF [C1206C106K3PACT U]	10 uF [C1210C106K4PACT U]
10 pF [C1206C100K1GACT U]	10 pF [CA064C100K1GAC TU]	10 uF [C1206C106K4PACT U]	10 uF [C1210C106K4RACT U]
10 pF [C1206C100K2GACT U]	10 pF [CA064C100K2GAC TU]	10 uF [C1206C106K4RACT U]	10 uF [C1210C106K8NAC TU]

Multisim 14.0 Full Components

10 uF [C1210C106K8PACT U]	10 uF [T491A106M016AT]	10 uF [T491D106M050AT]	10 uF [T494A106M010AT]
10 uF [C1210C106K8RACT U]	10 uF [T491A106M020AT]	10 uF [T491S106M004AT]	10 uF [T494A106M016AT]
10 uF [C1210C106K9PACT U]	10 uF [T491B106M004AT]	10 uF [T491S106M006AT]	10 uF [T494A106M020AT]
10 uF [C1210C106K9RACT U]	10 uF [T491B106M010AT]	10 uF [T491S106M010AT]	10 uF [T494B106M004AT]
10 uF [C1210C106K9RACT U]	10 uF [T491B106M016AT]	10 uF [T491T106M006AT]	10 uF [T494B106M006AT]
10 uF [C1210C106M4VAC TU]	10 uF [T491B106M020AT]	10 uF [T491T106M010AT]	10 uF [T494B106M010AT]
10 uF [C1210C106M8VAC TU]	10 uF [T491C106M010AT]	10 uF [T491T106M016AT]	10 uF [T494B106M020AT]
10 uF [C1210C106M9VAC TU]	10 uF [T491C106M016AT]	10 uF [T491U106M016AT]	10 uF [T494C106M010AT]
10 uF [T429E106M020AH 4250]	10 uF [T491C106M020AT]	10 uF [T491U106M020AT]	10 uF [T494C106M016AT]
10 uF [T429H106M035AH 4250]	10 uF [T491C106M025AT]	10 uF [T491V106M035AT]	10 uF [T494C106M020AT]
10 uF [T491A106M004AT]	10 uF [T491C106M035AT]	10 uF [T491X106M050AT]	10 uF [T494C106M025AT]
10 uF [T491A106M006AT]	10 uF [T491D106M025AT]	10 uF [T493C106M020AH 6110]	10 uF [T494C106M035AT]
10 uF [T491A106M010AT]	10 uF [T491D106M035AT]	10 uF [T494A106M004AT]	10 uF [T494D106M025AT]
		10 uF [T494A106M006AT]	10 uF [T494D106M035AT]

Multisim 14.0 Full Components

10 uF [T494D106M050AT]	10 uF [T495B106M020AT E1K0]	10 uF [T495X106M050AT E250]	10 uF [T498D106M035AT E700]
10 uF [T494S106M004AT]	10 uF [T495C106M020AT E400]	10 uF [T495X106M050AT E260]	10 uF [T498D106M050AT E1K0]
10 uF [T494S106M006AT]	10 uF [T495C106M020AT E475]	10 uF [T495X106M050AT E300]	10 uF [T510X106M050AT E090]
10 uF [T494S106M010AT]	10 uF [T495C106M025AT E275]	10 uF [T496D106M025AT 6110]	10 uF [T510X106M050AT E120]
10 uF [T494T106M006AT]	10 uF [T495C106M025AT E450]	10 uF [T497F106M015AT 6110]	10 uF [T520A106M010AT E080]
10 uF [T494T106M010AT]	10 uF [T495D106M035AT E125]	10 uF [T498B106M006AT E2K1]	10 uF [T520B106M016AT E100]
10 uF [T494U106M016AT]	10 uF [T495D106M035AT E250]	10 uF [T498B106M010AT E1K8]	10 uF [T521D106M050AT E090]
10 uF [T494U106M020AT]	10 uF [T495D106M035AT E300]	10 uF [T498B106M016AT E2K8]	10 uF [T521X106M063AT E050]
10 uF [T494V106M035AT]	10 uF [T495T106M016AT E4K0]	10 uF [T498C106M016AT E1K4]	10 uF [T541X106M063AH 6510]
10 uF [T494X106M050AT]	10 uF [T495X106M035AT E200]	10 uF [T498C106M020AT E1K1]	10_AMP
10 uF [T495A106M010AT E1K8]	10 uF [T495X106M035AT E250]	10 uF [T498C106M025AT E1K1]	100 nF [C0201C104K9PACT U]
10 uF [T495B106M010AT E750]			100 nF [C0402C104K4PACT U]

Multisim 14.0 Full Components

100 nF [C0402C104K4RACT U]	100 nF [C0603C104M4VAC TU]	100 nF [C0805C104M5VAC TU]	100 nF [C1206F104K1RACT U]
100 nF [C0402C104K8PACT U]	100 nF [C0603C104M8VAC TU]	100 nF [C1206C104K1RACT U]	100 nF [C1206F104K2RACT U]
100 nF [C0402C104K8RACT U]	100 nF [C0805C104K1RACT U]	100 nF [C1206C104K2RACT U]	100 nF [C1206F104K3RACT U]
100 nF [C0402C104K9PACT U]	100 nF [C0805C104K3RACT U]	100 nF [C1206C104K3GACT U]	100 nF [C1206F104K4RACT U]
100 nF [C0402C104K9RACT U]	100 nF [C0805C104K4RACT U]	100 nF [C1206C104K3HACT U]	100 nF [C1206F104K5RACT U]
100 nF [C0603C104K3RACT U]	100 nF [C0805C104K5RACT U]	100 nF [C1206C104K3RACT U]	100 nF [C1210C104K1GACT U]
100 nF [C0603C104K4RACT U]	100 nF [C0805C104K8RACT U]	100 nF [C1206C104K4RACT U]	100 nF [C1210C104K1HACT U]
100 nF [C0603C104K5RACT U]	100 nF [C0805C104K9RACT U]	100 nF [C1206C104K5RACT U]	100 nF [C1210C104K1RACT U]
100 nF [C0603C104K8RACT U]	100 nF [C0805C104M3VAC TU]	100 nF [C1206C104KARACT U]	100 nF [C1210C104K2RACT U]
100 nF [C0603C104K9RACT U]	100 nF [C0805C104M4VAC TU]	100 nF [C1206C104M1UAC TU]	100 nF [C1210C104K3GACT U]
100 nF [C0603C104M3VAC TU]	100 nF [C0805C104M5UAC TU]	100 nF [C1206C104M5UAC TU]	100 nF [C1210C104K3HACT U]

Multisim 14.0 Full Components

100 nF [C1210C104K3RACT U]	100 nF [C1210F104K3RACT U]	100 nF [C1812C104M1UAC TU]	100 nF [C2225C104K2RACT U]
100 nF [C1210C104K4RACT U]	100 nF [C1210F104K4RACT U]	100 nF [C1812F104K1RACT U]	100 nF [C2225C104K5RACT U]
100 nF [C1210C104K5GACT U]	100 nF [C1210F104K5RACT U]	100 nF [C1812F104K2RACT U]	100 nF [CA064C104K4RACT U]
100 nF [C1210C104K5HACT U]	100 nF [C1812C104K1GACT U]	100 nF [C1812F104K3RACT U]	100 nF [CA064C104K8RACT U]
100 nF [C1210C104K5RACT U]	100 nF [C1812C104K1HACT U]	100 nF [C1812F104K5RACT U]	100 nF [T491A104M035AT]
100 nF [C1210C104K8RACT U]	100 nF [C1812C104K1R1C7 186]	100 nF [C1825C104K1RACT U]	100 nF [T491A104M050AT]
100 nF [C1210C104KARACT U]	100 nF [C1812C104K1RACT U]	100 nF [C1825C104K2RACT U]	100 nF [T494A104M035AT]
100 nF [C1210C104M1UAC TU]	100 nF [C1812C104K2RACT U]	100 nF [C2220C104K1GACT U]	100 pF [03028BR101AKZC]
100 nF [C1210C104M5UAC TU]	100 nF [C1812C104K5GACT U]	100 nF [C2220C104K2GACT U]	100 pF [C0201C101K3GACT U]
100 nF [C1210F104K1RACT U]	100 nF [C1812C104K5HACT U]	100 nF [C2220C104K5GACT U]	100 pF [C0402C101K1HACT U]
100 nF [C1210F104K2RACT U]	100 nF [C1812C104K5RACT U]	100 nF [C2225C104K1RACT U]	100 pF [C0402C101K3GACT U]

Multisim 14.0 Full Components

100 pF [C0402C101K3HACT U]	100 pF [C0805C101K1GACT U]	100 pF [C1206C101K3GACT U]	100 pF [C1812C101KDGAC TU]
100 pF [C0402C101K4GACT U]	100 pF [C0805C101K2GACT U]	100 pF [C1206C101K5GACT U]	100 pF [C1812C101KHGAC TU]
100 pF [C0402C101K5GACT U]	100 pF [C0805C101K3GACT U]	100 pF [C1206C101KBGAC TU]	100 pF [C1825C101KBGAC TU]
100 pF [C0402C101K5HACT U]	100 pF [C0805C101K4GACT U]	100 pF [C1206C101KCGAC TU]	100 pF [C2220C101KBGAC TU]
100 pF [C0402C101K8GACT U]	100 pF [C0805C101K5GACT U]	100 pF [C1206C101KDGAC TU]	100 pF [C2225C101KBGAC TU]
100 pF [C0603C101K1GACT U]	100 pF [C0805C101KBGAC TU]	100 pF [C1206C101KGGAC TU]	100 pF [CA064C101K1GAC TU]
100 pF [C0603C101K3GACT U]	100 pF [C0805C101KCGAC TU]	100 pF [C1210C101K5GACT U]	100 pF [CA064C101K3GAC TU]
100 pF [C0603C101K4GACT U]	100 pF [C0805C101KDGAC TU]	100 pF [C1210C101KBGAC TU]	100 pF [CA064C101K5GAC TU]
100 pF [C0603C101K5GACT U]	100 pF [C0805H101K5GAC TU]	100 pF [C1210C101KCGAC TU]	100 pF [CA064C101K8GAC TU]
100 pF [C0603C101K5RACT U]	100 pF [C1206C101K1GACT U]	100 pF [C1210C101KDGAC TU]	100 uF [A700D107M006AT E015]
100 pF [C0603C101K8GACT U]	100 pF [C1206C101K2GACT U]	100 pF [C1812C101KBGAC TU]	100 uF [A700D107M006AT E018]

Multisim 14.0 Full Components

100 uF [A700V107M002AT E018]	100 uF [T491B107M006AT]	100 uF [T491U107M004AT]	100 uF [T494D107M004AT]
100 uF [A700V107M002AT E025]	100 uF [T491B107M010AT]	100 uF [T491U107M006AT]	100 uF [T494D107M006AT]
100 uF [A700V107M002AT E028]	100 uF [T491C107M004AT]	100 uF [T491V107M006AT]	100 uF [T494D107M010AT]
100 uF [A700X107M008AT E010]	100 uF [T491C107M010AT]	100 uF [T491V107M010AT]	100 uF [T494D107M016AT]
100 uF [A700X107M008AT E015]	100 uF [T491D107M004AT]	100 uF [T491V107M016AT]	100 uF [T494E107M020AT]
100 uF [A700X107M010AT E010]	100 uF [T491D107M006AT]	100 uF [T491X107M016AT]	100 uF [T494T107M004AT]
100 uF [A700X107M010AT E015]	100 uF [T491D107M010AT]	100 uF [T491X107M020AT]	100 uF [T494T107M025AT]
100 uF [T489C107M010AT E500]	100 uF [T491D107M016AT]	100 uF [T491X107M025AT]	100 uF [T494A107M004AT]
100 uF [T489D107M010AT E150]	100 uF [T491D107M020AT]	100 uF [T494A107M004AT]	100 uF [T494U107M004AT]
100 uF [T489D107M010AT E440]	100 uF [T491E107M020AT]	100 uF [T494B107M004AT]	100 uF [T494U107M006AT]
100 uF [T491A107M004AT]	100 uF [T491T107M004AT]	100 uF [T494B107M006AT]	100 uF [T494V107M006AT]
100 uF [T491B107M004AT]	100 uF [T491T107M2R5AT]	100 uF [T494C107M004AT]	100 uF [T494V107M010AT]
		100 uF [T494C107M006AT]	100 uF [T494V107M016AT]
		100 uF [T494C107M010AT]	100 uF [T494X107M016AT]

Multisim 14.0 Full Components

100 uF [T494X107M020AT]	100 uF [T495D107M016AT E100]	100 uF [T495X107M020AT E100]	100 uF [T520B107M003AT E035]
100 uF [T494X107M025AT]	100 uF [T495D107M016AT E125]	100 uF [T495X107M020AT E150]	100 uF [T520B107M003AT E040]
100 uF [T495B107M006AT E400]	100 uF [T495E107M020AT E060]	100 uF [T498D107M006AT E600]	100 uF [T520B107M003AT E070]
100 uF [T495B107M006AT E700]	100 uF [T495E107M020AT E200]	100 uF [T498D107M010AT E600]	100 uF [T520B107M004AT E035]
100 uF [T495B107M010AT E350]	100 uF [T495T107M2R5AT E3K0]	100 uF [T510E107M025AT E050]	100 uF [T520B107M004AT E040]
100 uF [T495C107M006AT E150]	100 uF [T495V107M006AT E150]	100 uF [T510X107M020AT E040]	100 uF [T520B107M004AT E070]
100 uF [T495D107M006AT E050]	100 uF [T495V107M010AT E100]	100 uF [T510X107M020AT E045]	100 uF [T520B107M006AT E015]
100 uF [T495D107M006AT E130]	100 uF [T495V107M010AT E150]	100 uF [T513D107M016AH 6110]	100 uF [T520B107M006AT E018]
100 uF [T495D107M010AT E050]	100 uF [T495X107M010AT E100]	100 uF [T513E107M025AH 6110]	100 uF [T520B107M006AT E025]
100 uF [T495D107M010AT E065]	100 uF [T495X107M016AT E080]	100 uF [T513X107M020AH 6110]	100 uF [T520B107M006AT E035]
100 uF [T495D107M010AT E080]	100 uF [T495X107M016AT E100]	100 uF [T513X107M020AH 6120]	100 uF [T520B107M006AT E040]

Multisim 14.0 Full Components

100 uF [T520B107M006AT E070]	100 uF [T520T107M004AT E070]	100 uF [T520V107M010AT E025]	100 uF [T525D107M010AT E055]
100 uF [T520B107M2R5AT E035]	100 uF [T520T107M004AT E150]	100 uF [T520V107M010AT E045]	100 uF [T525T107M2R5AT E080]
100 uF [T520B107M2R5AT E040]	100 uF [T520T107M006AT E070]	100 uF [T520V107M010AT E050]	100 uF [T528I107M003ATE 200]
100 uF [T520C107M006AT E025]	100 uF [T520T107M2R5AT E070]	100 uF [T520W107M006AT E040]	100 uF [T540B107M004AH 6510]
100 uF [T520C107M006AT E045]	100 uF [T520U107M004AT E055]	100 uF [T520W107M010AT E040]	100 uF [T540D107M010AH 6510]
100 uF [T520C107M010AT E025]	100 uF [T520U107M006AT E055]	100 uF [T521D107M016AT E050]	10029449-001RLF 100V_100W
100 uF [T520C107M010AT E045]	100 uF [T520V107M006AT E007]	100 uF [T521V107M016AT E050]	10104111-0001LF 105081-0001
100 uF [T520D107M006AT E007]	100 uF [T520V107M006AT E009]	100 uF [T521X107M025AT E060]	10Line_Bussed 10Line_Isolated
100 uF [T520D107M010AT E018]	100 uF [T520V107M006AT E012]	100 uF [T525B107M003AT E080]	11 pF [C0805C110KBGAC TU]
100 uF [T520D107M010AT E055]	100 uF [T520V107M006AT E045]	100 uF [T525B107M004AT E080]	11 pF [C1206C110KBGAC TU]
100 uF [T520D107M010AT E080]	100 uF [T520V107M010AT E018]	100 uF [T525D107M010AT E025]	11 pF [C1210C110KBGAC TU]

Multisim 14.0 Full Components

11 pF [C1812C110KBGAC TU]	110 pF [C1210C111KBGAC TU]	12 nF [C0603C123K1RACT U]	12 nF [C0805C123K5HACT U]
11 pF [C1825C110KBGAC TU]	110 pF [C1812C111KBGAC TU]	12 nF [C0603C123K3RACT U]	12 nF [C0805C123K5RACT U]
11 pF [C2220C110KBGAC TU]	110 pF [C1825C111KBGAC TU]	12 nF [C0603C123K4RACT U]	12 nF [C0805C123K8RACT U]
11 pF [C2225C110KBGAC TU]	110 pF [C2220C111KBGAC TU]	12 nF [C0603C123K5RACT U]	12 nF [C0805C123KARACT U]
110 pF [C0402C111K1HACT U]	110 pF [C2225C111KBGAC TU]	12 nF [C0805C123K1GACT U]	12 nF [C0805F123K1RACT U]
110 pF [C0402C111K3HACT U]	12 nF [C0402C123K4RACT U]	12 nF [C0805C123K1HACT U]	12 nF [C0805F123K3RACT U]
110 pF [C0402C111K5HACT U]	12 nF [C0402C123K5RACT U]	12 nF [C0805C123K1RACT U]	12 nF [C0805F123K4RACT U]
110 pF [C0603C111K5GACT U]	12 nF [C0402C123K8PACT U]	12 nF [C0805C123K3HACT U]	12 nF [C0805F123K5RACT U]
110 pF [C0805C111K1GACT U]	12 nF [C0402C123K8RACT U]	12 nF [C0805C123K3RACT U]	12 nF [C1206C123K1HACT U]
110 pF [C1206C111K5GACT U]	12 nF [C0402C123K9PACT U]	12 nF [C0805C123K4RACT U]	12 nF [C1206C123K1RACT U]
110 pF [C1206C111KBGAC TU]	12 nF [C0402C123K9RACT U]	12 nF [C0805C123K5GACT U]	12 nF [C1206C123K2RACT U]

Multisim 14.0 Full Components

12 nF [C1206C123K3HACT U]	12 nF [C1210C123KARACT U]	12 pF [C0805C120K5GACT U]	12 uF [C1210C126K8PACT U]
12 nF [C1206C123K5HACT U]	12 nF [C1812C123K1RACT U]	12 pF [C0805C120KBGAC TU]	120 nF [C0603C124K4RACT U]
12 nF [C1206C123K5RACT U]	12 nF [C2220C123K2GACT U]	12 pF [C1206C120K1GACT U]	120 nF [C0603C124K8RACT U]
12 nF [C1206C123KARACT U]	12 pF [C0201C120K3GACT U]	12 pF [C1206C120K5GACT U]	120 nF [C0805C124K1RACT U]
12 nF [C1210C123K1GACT U]	12 pF [C0402C120K4GACT U]	12 pF [C1206C120KBGAC TU]	120 nF [C0805C124K3RACT U]
12 nF [C1210C123K1HACT U]	12 pF [C0402C120K5GACT U]	12 pF [C1210C120KBGAC TU]	120 nF [C0805C124K4RACT U]
12 nF [C1210C123K3HACT U]	12 pF [C0603C120K1GACT U]	12 pF [C1812C120KBGAC TU]	120 nF [C0805C124K5RACT U]
12 nF [C1210C123K4RACT U]	12 pF [C0603C120K2GACT U]	12 pF [C1825C120KBGAC TU]	120 nF [C0805C124K8RACT U]
12 nF [C1210C123K5GACT U]	12 pF [C0603C120K3GACT U]	12 pF [C2220C120KBGAC TU]	120 nF [C1206C124K1RACT U]
12 nF [C1210C123K5HACT U]	12 pF [C0603C120K5GACT U]	12 pF [C2225C120KBGAC TU]	120 nF [C1206C124K2RACT U]
12 nF [C1210C123K5RACT U]	12 pF [C0805C120K1GACT U]	12 pF [CA064C120K5GAC TU]	120 nF [C1206C124K3RACT U]

Multisim 14.0 Full Components

120 nF [C1206C124K4RACT U]	120 nF [C1812C124K1GACT U]	120 nF [C2220C124K1GACT U]	120 pF [C0805C121K2GACT U]
120 nF [C1206C124K5RACT U]	120 nF [C1812C124K1HACT U]	120 nF [C2220C124K5GACT U]	120 pF [C0805C121K5GACT U]
120 nF [C1206C124M5UAC TU]	120 nF [C1812C124K2RACT U]	120 nF [C2225C124K1RACT U]	120 pF [C1206C121K1GACT U]
120 nF [C1210C124K1RACT U]	120 nF [C1812C124K5GACT U]	120 pF [03029BR121AKZC]	120 pF [C1206C121K2GACT U]
120 nF [C1210C124K3HACT U]	120 nF [C1812C124K5HACT U]	120 pF [C0402C121K1HACT U]	120 pF [C1206C121K5GACT U]
120 nF [C1210C124K5HACT U]	120 nF [C1812C124K5RACT U]	120 pF [C0402C121K3HACT U]	120 pF [C1206C121KBGAC TU]
120 nF [C1210C124K5RACT U]	120 nF [C1812C124M1UAC TU]	120 pF [C0402C121K5GACT U]	120 pF [C1206C121KDGAC TU]
120 nF [C1210F124K1RACT U]	120 nF [C1812F124K1RACT U]	120 pF [C0402C121K5HACT U]	120 pF [C1210C121KBGAC TU]
120 nF [C1210F124K3RACT U]	120 nF [C1812F124K2RACT U]	120 pF [C0603C121K1GACT U]	120 pF [C1812C121KBGAC TU]
120 nF [C1210F124K4RACT U]	120 nF [C1812F124K3RACT U]	120 pF [C0603C121K5GACT U]	120 pF [C1825C121KBGAC TU]
120 nF [C1210F124K5RACT U]	120 nF [C1812F124K5RACT U]	120 pF [C0805C121K1GACT U]	120 pF [C2220C121KBGAC TU]

Multisim 14.0 Full Components

120 pF [C2225C121KBGAC TU]	120V_250W 1-282834-0	13 pF [C2220C130KBGAC TU]	130 pF [C2225C131KBGAC TU]
120 pF [CA064C121K5GAC TU]	12A02CH-TL-E 12A02MH-TL-E	13 pF [C2225C130KBGAC TU]	15 nF [C0402C153K4RACT U]
120 uF [A700D127M004AT E015]	12V_10W 12V_25W	130 pF [C0402C131K1HACT U]	15 nF [C0402C153K5RACT U]
120 uF [A700D127M004AT E018]	13 pF [C0603C130K2GACT U]	130 pF [C0402C131K3HACT U]	15 nF [C0402C153K8PACT U]
120 uF [A700D127M006AT E012]	13 pF [C0603C130K5GACT U]	130 pF [C0402C131K5HACT U]	15 nF [C0402C153K8RACT U]
120 uF [A700D127M006AT E015]	13 pF [C0805C130K5GACT U]	130 pF [C0805H131K3GAC TU]	15 nF [C0402C153K9PACT U]
120 uF [A700D127M006AT E018]	13 pF [C0805C130KBGAC TU]	130 pF [C1206C131KBGAC TU]	15 nF [C0402C153K9RACT U]
120 uF [A700V127M002AT E018]	13 pF [C1206C130KBGAC TU]	130 pF [C1210C131KBGAC TU]	15 nF [C0603C153K1RACT U]
120 uF [A700X127M010AT E010]	13 pF [C1210C130KBGAC TU]	130 pF [C1812C131KBGAC TU]	15 nF [C0603C153K3RACT U]
120 uF [A700X127M010AT E015]	13 pF [C1812C130KBGAC TU]	130 pF [C1825C131KBGAC TU]	15 nF [C0603C153K4RACT U]
120 uF [T520B127M006AT E035]	13 pF [C1825C130KBGAC TU]	130 pF [C2220C131KBGAC TU]	15 nF [C0603C153K5RACT U]

120V_100W

Multisim 14.0 Full Components

15 nF [C0805C153K1GACT U]	15 nF [C0805C153M5UAC TU]	15 nF [C1206C153K5RACT U]	15 nF [C1812C153K1GACT U]
15 nF [C0805C153K1HACT U]	15 nF [C0805F153K1RACT U]	15 nF [C1206C153KARACT U]	15 nF [C1812C153K1HACT U]
15 nF [C0805C153K1RACT U]	15 nF [C0805F153K3RACT U]	15 nF [C1206C153M5UAC TU]	15 nF [C1812C153K1RACT U]
15 nF [C0805C153K3HACT U]	15 nF [C0805F153K4RACT U]	15 nF [C1210C153K1GACT U]	15 nF [C1812C153K2RACT U]
15 nF [C0805C153K3RACT U]	15 nF [C0805F153K5RACT U]	15 nF [C1210C153K1HACT U]	15 nF [C1812C153K5GACT U]
15 nF [C0805C153K4RACT U]	15 nF [C1206C153K1HACT U]	15 nF [C1210C153K1RACT U]	15 nF [C1812C153K5HACT U]
15 nF [C0805C153K5GACT U]	15 nF [C1206C153K1RACT U]	15 nF [C1210C153K2RACT U]	15 nF [C1812C153K5RACT U]
15 nF [C0805C153K5HACT U]	15 nF [C1206C153K2RACT U]	15 nF [C1210C153K3HACT U]	15 nF [C1825C153K5GACT U]
15 nF [C0805C153K5RACT U]	15 nF [C1206C153K3HACT U]	15 nF [C1210C153K5HACT U]	15 nF [C2220C153K2GACT U]
15 nF [C0805C153K8RACT U]	15 nF [C1206C153K4RACT U]	15 nF [C1210C153K5RACT U]	15 nF [C2225C153K5GACT U]
15 nF [C0805C153KARACT U]	15 nF [C1206C153K5HACT U]	15 nF [C1210C153KARACT U]	15 nF [CA064C153K5RACT U]

Multisim 14.0 Full Components

15 pF [C0201C150K3GACT U]	15 pF [C0805C150K3GACT U]	15 pF [C1825C150KBGAC TU]	15 uF [T419B156M004AH 4250]
15 pF [C0402C150K3GACT U]	15 pF [C0805C150K4GACT U]	15 pF [C2220C150KBGAC TU]	15 uF [T419D156M010AH 4250]
15 pF [C0402C150K4GACT U]	15 pF [C0805C150K5GACT U]	15 pF [C2225C150KBGAC TU]	15 uF [T429B156M004AH 4250]
15 pF [C0402C150K5GACT U]	15 pF [C0805C150KBGAC TU]	15 pF [CA064C150K4GAC TU]	15 uF [T429F156M010AH 4250]
15 pF [C0402C150K8GACT U]	15 pF [C1206C150K1GACT U]	15 pF [CA064C150K5GAC TU]	15 uF [T429F156M020AH 4250]
15 pF [C0603C150K1GACT U]	15 pF [C1206C150K2GACT U]	15 uF [A700V156M12RAT E040]	15 uF [T489D156M025AT E300]
15 pF [C0603C150K2GACT U]	15 pF [C1206C150K5GACT U]	15 uF [C1210C156K4PACT U]	15 uF [T491A156M004AT]
15 pF [C0603C150K4GACT U]	15 pF [C1206C150KBGAC TU]	15 uF [C1210C156K8PACT U]	15 uF [T491A156M006AT]
15 pF [C0603C150K5GACT U]	15 pF [C1206C150KGGAC TU]	15 uF [C1210C156K9PACT U]	15 uF [T491A156M010AT]
15 pF [C0805C150K1GACT U]	15 pF [C1210C150KBGAC TU]	15 uF [T409E156M004AH 4250]	15 uF [T491B156M004AT]
15 pF [C0805C150K2GACT U]	15 pF [C1812C150KBGAC TU]	15 uF [T409H156M025AH 4250]	15 uF [T491B156M006AT]
			15 uF [T491B156M010AT]
			15 uF [T491B156M016AT]

Multisim 14.0 Full Components

15 uF [T491B156M025AT]	15 uF [T491U156M016AT]	15 uF [T494C156M025AT]	15 uF [T495B156M010AT E500]
15 uF [T491C156M006AT]	15 uF [T491X156M035AT]	15 uF [T494D156M020AT]	15 uF [T495C156M010AT E375]
15 uF [T491C156M010AT]	15 uF [T491X156M050AT]	15 uF [T494D156M025AT]	15 uF [T495C156M010AT E400]
15 uF [T491C156M016AT]	15 uF [T494A156M004AT]	15 uF [T494D156M035AT]	15 uF [T495D156M020AT E275]
15 uF [T491C156M025AT]	15 uF [T494A156M006AT]	15 uF [T494S156M004AT]	15 uF [T495D156M025AT E100]
15 uF [T491D156M020AT]	15 uF [T494A156M010AT]	15 uF [T494S156M006AT]	15 uF [T495D156M025AT E275]
15 uF [T491D156M025AT]	15 uF [T494B156M004AT]	15 uF [T494T156M004AT]	15 uF [T495D156M035AT E225]
15 uF [T491D156M035AT]	15 uF [T494B156M010AT]	15 uF [T494T156M006AT]	15 uF [T495D156M035AT E300]
15 uF [T491S156M004AT]	15 uF [T494B156M016AT]	15 uF [T494T156M010AT]	15 uF [T495X156M025AT E200]
15 uF [T491S156M006AT]	15 uF [T494B156M025AT]	15 uF [T494U156M010AT]	15 uF [T495X156M035AT E200]
15 uF [T491T156M004AT]	15 uF [T494C156M006AT]	15 uF [T494U156M016AT]	15 uF [T495X156M050AT E200]
15 uF [T491T156M006AT]	15 uF [T494C156M010AT]	15 uF [T494X156M035AT]	
15 uF [T491T156M010AT]	15 uF [T494C156M016AT]	15 uF [T494X156M050AT]	
15 uF [T491U156M010AT]	15 uF [T494C156M020AT]		

Multisim 14.0 Full Components

15 uF [T495X156M050AT E300]	15 uF [T520D156M025AT E060]	15 uF [T541X156M063AH 6510]	150 nF [C0805C154K8RACT U]
15 uF [T497E156M010AT 6110]	15 uF [T520D156M025AT E080]	15 uF [T543T156M006AT E100]	150 nF [C0805C154M3VAC TU]
15 uF [T498B156M006AT E1K8]	15 uF [T520T156M004AT E100]	15_AMP 150 nF [C0603C154K4RACT U]	150 nF [C1206C154K1RACT U]
15 uF [T498B156M010AT E1K5]	15 uF [T520T156M006AT E100]	150 nF [C0603C154K5RACT U]	150 nF [C1206C154K2RACT U]
15 uF [T498C156M010AT E1K8]	15 uF [T520T156M12RAT E080]	150 nF [C0603C154K8RACT U]	150 nF [C1206C154K3RACT U]
15 uF [T498C156M016AT E1K1]	15 uF [T521B156M016AT E090]	150 nF [C0603C154M3VAC TU]	150 nF [C1206C154K4RACT U]
15 uF [T498D156M025AT E700]	15 uF [T521V156M025AT E090]	150 nF [C0603C154M4VAC TU]	150 nF [C1206C154K5RACT U]
15 uF [T499B156M006AT E3K5]	15 uF [T521V156M035AT E100]	150 nF [C0603C154M8VAC TU]	150 nF [C1206C154M5UAC TU]
15 uF [T499D156M020AT E1K0]	15 uF [T521V156M035AT E125]	150 nF [C0805C154K3RACT U]	150 nF [C1206F154K1RACT U]
15 uF [T513D156M035AH 6110]	15 uF [T521X156M063AT E035]	150 nF [C0805C154K4RACT U]	150 nF [C1206F154K3RACT U]
15 uF [T520A156M010AT E080]	15 uF [T521X156M063AT E150]	150 nF [C0805C154K5RACT U]	150 nF [C1206F154K4RACT U]

Multisim 14.0 Full Components

150 nF [C1206F154K5RACT U]	150 nF [C1812C154K1RACT U]	150 nF [C1825C154K1RACT U]	150 pF [C0402C151K1HACT U]
150 nF [C1210C154K1RACT U]	150 nF [C1812C154K2RACT U]	150 nF [C1825C154K5RACT U]	150 pF [C0402C151K3HACT U]
150 nF [C1210C154K3HACT U]	150 nF [C1812C154K5GACT U]	150 nF [C2220C154K1GACT U]	150 pF [C0402C151K3RACT U]
150 nF [C1210C154K5HACT U]	150 nF [C1812C154K5HACT U]	150 nF [C2220C154K5GACT U]	150 pF [C0402C151K4RACT U]
150 nF [C1210C154K5RACT U]	150 nF [C1812C154K5RACT U]	150 nF [C2225C154K1RACT U]	150 pF [C0402C151K5GACT U]
150 nF [C1210F154K1RACT U]	150 nF [C1812C154M1UAC TU]	150 nF [C2225C154K2RACT U]	150 pF [C0402C151K5HACT U]
150 nF [C1210F154K3RACT U]	150 nF [C1812C154M5UAC TU]	150 nF [T429A154M050AH 4250]	150 pF [C0402C151K5RACT U]
150 nF [C1210F154K4RACT U]	150 nF [C1812F154K1RACT U]	150 nF [T491A154M035AT]	150 pF [C0402C151K8RACT U]
150 nF [C1210F154K5RACT U]	150 nF [C1812F154K2RACT U]	150 nF [T491A154M050AT]	150 pF [C0603C151K1GACT U]
150 nF [C1812C154K1GACT U]	150 nF [C1812F154K3RACT U]	150 nF [T491B154M050AT]	150 pF [C0603C151K3GACT U]
150 nF [C1812C154K1HACT U]	150 nF [C1812F154K5RACT U]	150 nF [T494A154M035AT]	150 pF [C0603C151K3GACT U]
		150 nF [T494A154M050AT]	150 pF [C0603C151K4GACT U]
		150 nF [T494B154M050AT]	

Multisim 14.0 Full Components

150 pF [C0603C151K5GACT U]	150 pF [C1812C151KBGAC TU]	150 uF [A700V157M002AT E018]	150 uF [T491C157M010AT]
150 pF [C0805C151K1GACT U]	150 pF [C1825C151KBGAC TU]	150 uF [A700V157M002AT E025]	150 uF [T491D157M004AT]
150 pF [C0805C151K2GACT U]	150 pF [C2220C151KBGAC TU]	150 uF [A700V157M002AT E028]	150 uF [T491D157M006AT]
150 pF [C0805C151K3GACT U]	150 pF [C2225C151KBGAC TU]	150 uF [A700X157M006AT E010]	150 uF [T491D157M010AT]
150 pF [C0805C151K4GACT U]	150 pF [CA064C151K4GAC TU]	150 uF [A700X157M006AT E015]	150 uF [T491D157M016AT]
150 pF [C0805C151K5GACT U]	150 pF [CA064C151K5GAC TU]	150 uF [A700X157M010AT E010]	150 uF [T491V157M004AT]
150 pF [C1206C151K1GACT U]	150 uF [A700D157M004AT E015]	150 uF [A700X157M010AT E015]	150 uF [T491V157M006AT]
150 pF [C1206C151K2GACT U]	150 uF [A700D157M004AT E018]	150 uF [T429G157M006AH 4250]	150 uF [T491X157M010AT]
150 pF [C1206C151K5GACT U]	150 uF [A700D157M2R5AT E015]	150 uF [T429X157M010AH 4250]	150 uF [T491X157M016AT]
150 pF [C1206C151KBGAC TU]	150 uF [A700D157M2R5AT E018]	150 uF [T491B157M004AT]	150 uF [T494B157M004AT]
150 pF [C1210C151KBGAC TU]	150 uF [A700V157M002AT E009]	150 uF [T491C157M004AT]	150 uF [T494C157M004AT]
		150 uF [T491C157M006AT]	150 uF [T494C157M006AT]

Multisim 14.0 Full Components

150 uF [T494C157M010AT]	150 uF [T495D157M006AT E050]	150 uF [T495X157M010AT E085]	150 uF [T520B157M003AT E070]
150 uF [T494D157M004AT]	150 uF [T495D157M006AT E125]	150 uF [T495X157M010AT E100]	150 uF [T520B157M004AT E015]
150 uF [T494D157M006AT]	150 uF [T495D157M010AT E050]	150 uF [T495X157M016AT E075]	150 uF [T520B157M004AT E018]
150 uF [T494D157M010AT]	150 uF [T495D157M010AT E060]	150 uF [T495X157M016AT E100]	150 uF [T520B157M004AT E025]
150 uF [T494D157M016AT]	150 uF [T495D157M010AT E100]	150 uF [T510X157M016AT E030]	150 uF [T520B157M004AT E030]
150 uF [T494V157M004AT]	150 uF [T495D157M016AT E060]	150 uF [T510X157M016AT E040]	150 uF [T520B157M004AT E035]
150 uF [T494V157M006AT]	150 uF [T495D157M016AT E085]	150 uF [T513X157M016AH 6110]	150 uF [T520B157M004AT E040]
150 uF [T494X157M010AT]	150 uF [T495D157M016AT E100]	150 uF [T513X157M016AH 6120]	150 uF [T520B157M004AT E070]
150 uF [T494X157M016AT]	150 uF [T495D157M016AT E125]	150 uF [T520B157M003AT E025]	150 uF [T520B157M006AT E035]
150 uF [T495B157M004AT E900]	150 uF [T495D157M016AT E150]	150 uF [T520B157M003AT E035]	150 uF [T520B157M006AT E045]
150 uF [T495C157M006AT E200]	150 uF [T495V157M010AT E150]	150 uF [T520B157M003AT E040]	150 uF [T520B157M006AT E070]

Multisim 14.0 Full Components

150 uF [T520C157M004AT E015]	150 uF [T520D157M006AT E007]	150 uF [T520L157M006AT E025]	150 uF [T520V157M006AT E006]
150 uF [T520C157M004AT E025]	150 uF [T520D157M006AT E015]	150 uF [T520M157M006AT E070]	150 uF [T520V157M006AT E007]
150 uF [T520C157M004AT E045]	150 uF [T520D157M006AT E025]	150 uF [T520U157M004AT E055]	150 uF [T520V157M006AT E009]
150 uF [T520C157M004AT E100]	150 uF [T520D157M006AT E055]	150 uF [T520U157M006AT E045]	150 uF [T520V157M006AT E012]
150 uF [T520C157M006AT E015]	150 uF [T520D157M008AT E025]	150 uF [T520U157M006AT E055]	150 uF [T520V157M006AT E015]
150 uF [T520C157M006AT E025]	150 uF [T520D157M008AT E040]	150 uF [T520U157M2R5AT E055]	150 uF [T520V157M006AT E018]
150 uF [T520C157M006AT E045]	150 uF [T520D157M008AT E055]	150 uF [T520V157M004AT E007]	150 uF [T520V157M006AT E025]
150 uF [T520C157M006AT E055]	150 uF [T520D157M010AT E025]	150 uF [T520V157M004AT E009]	150 uF [T520V157M006AT E040]
150 uF [T520C157M010AT E055]	150 uF [T520D157M010AT E040]	150 uF [T520V157M004AT E012]	150 uF [T520V157M006AT E045]
150 uF [T520D157M004AT E007]	150 uF [T520D157M010AT E055]	150 uF [T520V157M004AT E015]	150 uF [T520V157M010AT E018]
150 uF [T520D157M006AT E006]	150 uF [T520L157M006AT E012]	150 uF [T520V157M004AT E025]	150 uF [T520V157M010AT E040]

Multisim 14.0 Full Components

150 uF [T520W157M006AT E025]	150 uF [T530D157M010AT E006]	16 pF [C1210C160KBGAC TU]	160 pF [C1210C161KBGAC TU]
150 uF [T520W157M006AT E040]	150 uF [T530D157M010AT E010]	16 pF [C1812C160KBGAC TU]	160 pF [C1812C161KBGAC TU]
150 uF [T520X157M016AT E040]	150 uF [T530X157M016AT E015]	16 pF [C1825C160KBGAC TU]	160 pF [C1825C161KBGAC TU]
150 uF [T522V157M006AT E040]	150 uF [T530X157M016AT E025]	16 pF [C2220C160KBGAC TU]	160 pF [C2220C161KBGAC TU]
150 uF [T525B157M003AT E080]	150 uF [T530X157M016AT E040]	16 pF [C2225C160KBGAC TU]	160 pF [C2225C161KBGAC TU]
150 uF [T525D157M006AT E025]	1-534206-0 1-534206-3	160 pF [C0402C161K1HACT U]	1-640455-0 171-009-113R001
150 uF [T525D157M010AT E025]	1-534206-7 15C02MH-TL-E	160 pF [C0402C161K3HACT U]	171-009-213R001 171-015-113R001
150 uF [T528Z157M006AT E007]	16 pF [C0603C160K2GACT U]	160 pF [C0402C161K5HACT U]	171-015-213R001 171-025-113R001
150 uF [T528Z157M006AT E008]	16 pF [C0603C160K5GACT U]	160 pF [C0805C161K3GACT U]	171-025-213R001 171-037-113R001
150 uF [T528Z157M006AT E009]	16 pF [C0805C160KBGAC TU]	160 pF [C0805C161K5GACT U]	171-037-213R001 171-050-113R001
150 uF [T528Z157M006AT E012]	16 pF [C1206C160KBGAC TU]	160 pF [C1206C161KBGAC TU]	171-050-213R001 1734035-1 173-E09-113R001 173-E09-213R001

Multisim 14.0 Full Components

173-E15-113R001	18 nF [C0402C183K9PACT U]	18 nF [C0805C183K5HACT U]	18 nF [C1206C183K3GACT U]
173-E15-213R001			
173-E25-113R001	18 nF [C0402C183K9RACT U]	18 nF [C0805C183K5RACT U]	18 nF [C1206C183K3HACT U]
173-E25-213R001			
173-E37-113R001	18 nF [C0603C183K1RACT U]	18 nF [C0805C183K8RACT U]	18 nF [C1206C183K5HACT U]
173-E37-213R001			
173-E50-113R001	18 nF [C0603C183K3RACT U]	18 nF [C0805C183KARACT U]	18 nF [C1206C183K5RACT U]
173-E50-213R001			
174-E09-113R001	18 nF [C0603C183K4RACT U]	18 nF [C0805F183K1RACT U]	18 nF [C1210C183K1GACT U]
174-E09-213R001			
174-E15-113R001	18 nF [C0603C183K5RACT U]	18 nF [C0805F183K3RACT U]	18 nF [C1210C183K1HACT U]
174-E15-213R001			
174-E25-113R001	18 nF [C0603C183K8RACT U]	18 nF [C0805F183K4RACT U]	18 nF [C1210C183K3HACT U]
174-E25-213R001			
174-E37-113R001	18 nF [C0805C183K1RACT U]	18 nF [C0805F183K5RACT U]	18 nF [C1210C183K5GACT U]
174-E37-213R001			
174-E50-113R001	18 nF [C0805C183K3GACT U]	18 nF [C1206C183K1HACT U]	18 nF [C1210C183K5HACT U]
174-E50-213R001			
18 nF [C0402C183K4RACT U]	18 nF [C0805C183K3HACT U]	18 nF [C1206C183K1RACT U]	18 nF [C1210C183K5RACT U]
18 nF [C0402C183K8PACT U]			
18 nF [C0402C183K8RACT U]	18 nF [C0805C183K4RACT U]	18 nF [C1206C183K2RACT U]	18 nF [C1210C183KARACT U]

Multisim 14.0 Full Components

18 nF [C1812C183K1GACT U]	18 pF [C0603C180K2GACT U]	18 pF [C1206C180KBGAC TU]	180 nF [C0603C184K8RACT U]
18 nF [C1812C183K1HACT U]	18 pF [C0603C180K3GACT U]	18 pF [C1210C180KBGAC TU]	180 nF [C0805C184K3RACT U]
18 nF [C1812C183K5GACT U]	18 pF [C0603C180K5GACT U]	18 pF [C1812C180KBGAC TU]	180 nF [C0805C184K4RACT U]
18 nF [C1812C183K5HACT U]	18 pF [C0603C180K8GACT U]	18 pF [C1825C180KBGAC TU]	180 nF [C0805C184K5RACT U]
18 nF [C2220C183K2GACT U]	18 pF [C0805C180K1GACT U]	18 pF [C2220C180KBGAC TU]	180 nF [C0805C184K8RACT U]
18 nF [CA064C183K3RAC]	18 pF [C0805C180K2GACT U]	18 pF [C2225C180KBGAC TU]	180 nF [C1206C184K1RACT U]
18 nF [CDR03BX183BKSM]	18 pF [C0805C180K3GACT U]	18 uF [C1210C186K4PACT U]	180 nF [C1206C184K5RACT U]
18 pF [C0201C180K3GACT U]	18 pF [C0805C180K5GACT U]	18 uF [C1210C186K8PACT U]	180 nF [C1206C184M5UAC TU]
18 pF [C0402C180K3GACT U]	18 pF [C0805C180KBGAC TU]	18 uF [C1210C186K9PACT U]	180 nF [C1206F184K1RACT U]
18 pF [C0402C180K5GACT U]	18 pF [C1206C180K1GACT U]	18 uF [T521X186M050AT E070]	180 nF [C1206F184K3RACT U]
18 pF [C0402C180K8GACT U]	18 pF [C1206C180K5GACT U]	180 nF [C0603C184K4RACT U]	180 nF [C1206F184K4RACT U]

Multisim 14.0 Full Components

180 nF [C1206F184K5RACT U]	180 nF [C1812F184K1RACT U]	180 pF [C0402C181K5RACT U]	180 pF [C0805C181K5GACT U]
180 nF [C1210C184K1RACT U]	180 nF [C1812F184K2RACT U]	180 pF [C0402C181K8RACT U]	180 pF [C1206C181K1GACT U]
180 nF [C1210C184K3HACT U]	180 nF [C1812F184K3RACT U]	180 pF [C0603C181K1RACT U]	180 pF [C1206C181K2GACT U]
180 nF [C1210C184K5RACT U]	180 nF [C1812F184K5RACT U]	180 pF [C0603C181K2RACT U]	180 pF [C1206C181K5GACT U]
180 nF [C1210F184K1RACT U]	180 nF [C1825C184K5RACT U]	180 pF [C0603C181K3RACT U]	180 pF [C1206C181KBGAC TU]
180 nF [C1210F184K3RACT U]	180 nF [C2225C184K1RACT U]	180 pF [C0603C181K4RACT U]	180 pF [C1210C181KBGAC TU]
180 nF [C1210F184K4RACT U]	180 pF [C0402C181K1HACT U]	180 pF [C0603C181K5GACT U]	180 pF [C1812C181KBGAC TU]
180 nF [C1210F184K5RACT U]	180 pF [C0402C181K3HACT U]	180 pF [C0603C181K5RACT U]	180 pF [C1825C181KBGAC TU]
180 nF [C1812C184K1RACT U]	180 pF [C0402C181K3RACT U]	180 pF [C0603C181K8RACT U]	180 pF [C2220C181KBGAC TU]
180 nF [C1812C184K5HACT U]	180 pF [C0402C181K4RACT U]	180 pF [C0805C181K1GACT U]	180 pF [C2225C181KBGAC TU]
180 nF [C1812C184K5RACT U]	180 pF [C0402C181K5HACT U]	180 pF [C0805C181K2GACT U]	180 pF [CA064C181K4GAC TU]

Multisim 14.0 Full Components

180 pF [CA064C181K5GAC TU]	181-026-213R431	1B4B42	1N3660
	181-044-113R431	1BH62	1N3661
180 uF [A700D187M002AT E015]	181-044-213R431	1DH62	1N3662
	181-062-113R431	1G4B42	1N3663
180 uF [A700D187M002AT E018]	181-062-213R431	1GH62	1N3879
	181-078-113R431	1J4B42	1N3879A
	181-078-213R431	1JH62	1N3880
180 uF [A700D187M004AT E015]	182-009-113R431	1LH62	1N3880A
	182-009-213R431	1N1199C	1N3881
180 uF [A700D187M004AT E018]	182-015-113R431	1N1200C	1N3881A
	182-015-213R431	1N1202C	1N3882
180 uF [A700D187M2R5AT E015]	182-025-113R431	1N1204C	1N3882A
	182-025-213R431	1N1206C	1N3883
180 uF [A700D187M2R5AT E018]	182-037-113R431	1N3064	1N3883A
	182-037-213R431	1N3208	1N3889
	183-009-113R161	1N3491	1N3889A
180 uF [A700X187M004AT E010]	183-009-213R161	1N3492	1N3890
	183-015-113R161	1N3493	1N3890A
180 uF [A700X187M006AT E010]	183-015-213R161	1N3494	1N3891
	183-025-113R161	1N3495	1N3891A
180 uF [A700X187M006AT E015]	183-025-213R161	1N3611GP	1N3892
	183-037-113R161	1N3612GP	1N3892A
181-015-113R431	183-037-213R161	1N3613GP	1N3893
181-015-213R431	1932258-1	1N3614GP	1N3893A
181-026-113R431	1981584-1	1N3659	1N3899

Multisim 14.0 Full Components

1N3900	1N4006FFG	1N4372A	1N4740A
1N3901	1N4006G	1N4383GP	1N4741A
1N3902	1N4006GP	1N4384GP	1N4742A
1N3903	1N4006RLG	1N4385GP	1N4743A
1N3909	1N4007-E3/54	1N4446	1N4744A
1N3910	1N4007FFG	1N4447	1N4745A
1N3911	1N4007G	1N4448	1N4746A
1N3912	1N4007GP	1N4449	1N4747A
1N3913	1N4007RLG	1N4454	1N4748A
1N3957GP	1N4009	1N4585GP	1N4749A
1N4001G	1N4148	1N4586GP	1N4750A
1N4001GP	1N4149	1N4678	1N4751A
1N4001RLG	1N4150	1N4681	1N4752A
1N4002G	1N4151	1N4728A	1N4753A
1N4002GP	1N4152	1N4729A	1N4754A
1N4002RLG	1N4153	1N4730A	1N4755A
1N4003G	1N4154	1N4731A	1N4756A
1N4003GP	1N4245GP	1N4732A	1N4757A
1N4003RLG	1N4246GP	1N4733A	1N4758A
1N4004G	1N4247GP	1N4734A	1N4759A
1N4004GP	1N4248GP	1N4735A	1N4760A
1N4004RLG	1N4249GP	1N4736A	1N4761A
1N4005G	1N4305	1N4737A	1N4762A
1N4005GP	1N4370A	1N4738A	1N4763A
1N4005RLG	1N4371A	1N4739A	1N4764A

Multisim 14.0 Full Components

1N4933	1N5221B	1N5246B	1N5271B
1N4933G	1N5222B	1N5247B	1N5272B
1N4933RLG	1N5223B	1N5248B	1N5273B
1N4934	1N5224B	1N5249B	1N5274B
1N4934G	1N5225B	1N5250B	1N5275B
1N4934RLG	1N5226B	1N5251B	1N5276B
1N4935	1N5227B	1N5252B	1N5277B
1N4935G	1N5228B	1N5253B	1N5278B
1N4935RLG	1N5229B	1N5254B	1N5279B
1N4936	1N5230B	1N5255B	1N5280B
1N4936G	1N5231B	1N5256B	1N5281B
1N4936RLG	1N5232B	1N5257B	1N5333BRLG
1N4937	1N5233B	1N5258B	1N5334BRLG
1N4937G	1N5234B	1N5259B	1N5335BG
1N4937RLG	1N5235B	1N5260B	1N5335BRLG
1N4938	1N5236B	1N5261B	1N5336BG
1N4942GP	1N5237B	1N5262B	1N5336BRLG
1N4944GP	1N5238B	1N5263B	1N5337BG
1N4946GP	1N5239B	1N5264B	1N5337BRLG
1N4947GP	1N5240B	1N5265B	1N5338BG
1N4948GP	1N5241B	1N5266B	1N5338BRLG
1N5059GP	1N5242B	1N5267B	1N5339BG
1N5060GP	1N5243B	1N5268B	1N5339BRLG
1N5061GP	1N5244B	1N5269B	1N5340BG
1N5062GP	1N5245B	1N5270B	1N5340BRLG

Multisim 14.0 Full Components

1N5341BG	1N5355BG	1N5369BG	1N5393GP
1N5341BRLG	1N5355BRLG	1N5369BRLG	1N5394GP
1N5342BG	1N5356BRLG	1N5371BRLG	1N5395GP
1N5342BRLG	1N5357BG	1N5372BG	1N5396GP
1N5343BG	1N5357BRLG	1N5372BRLG	1N5397GP
1N5343BRLG	1N5358BG	1N5373BG	1N5398GP
1N5344BG	1N5358BRLG	1N5373BRLG	1N5399GP
1N5344BRLG	1N5359BG	1N5374BG	1N5400
1N5345BRLG	1N5359BRLG	1N5374BRLG	1N5400G
1N5346BG	1N5361BG	1N5375BG	1N5400RLG
1N5346BRLG	1N5361BRLG	1N5375BRLG	1N5401
1N5347BG	1N5362BG	1N5378BG	1N5401G
1N5347BRLG	1N5362BRLG	1N5378BRLG	1N5401RLG
1N5348BG	1N5363BG	1N5381BRLG	1N5402
1N5348BRLG	1N5363BRLG	1N5383BG	1N5402G
1N5349BG	1N5364BG	1N5383BRLG	1N5402RLG
1N5349BRLG	1N5364BRLG	1N5384BG	1N5404
1N5350BG	1N5365BG	1N5384BRLG	1N5404G
1N5350BRLG	1N5365BRLG	1N5386BG	1N5404RLG
1N5351BG	1N5366BG	1N5386BRLG	1N5406
1N5351BRLG	1N5366BRLG	1N5388BG	1N5406G
1N5352BG	1N5367BG	1N5388BRLG	1N5406RLG
1N5352BRLG	1N5367BRLG	1N5391	1N5407G
1N5353BG	1N5368BG	1N5391GP	1N5407RLG
1N5353BRLG	1N5368BRLG	1N5392GP	1N5408-E3/54

Multisim 14.0 Full Components

1N5408G	1N5821G	1N5919B	1N5931BRLG
1N5408RLG	1N5821RLG	1N5919BG	1N5932B
1N5615GP	1N5822	1N5919BRLG	1N5932BRLG
1N5617GP	1N5822-E3/54	1N5920B	1N5933B
1N5619GP	1N5822G	1N5920BG	1N5934B
1N5621GP	1N5822RLG	1N5921B	1N5934BG
1N5623GP	1N5823	1N5921BG	1N5934BRLG
1N5758	1N5824	1N5921BRLG	1N5935B
1N5758A	1N5825	1N5922B	1N5935BRLG
1N5759	1N5826	1N5923B	1N5936B
1N5759A	1N5827	1N5923BRLG	1N5937B
1N5760	1N5828	1N5924B	1N5937BRLG
1N5761	1N5829	1N5924BRLG	1N5938B
1N5761A	1N5830	1N5925B	1N5938BRLG
1N5817-E3/54	1N5831	1N5925BRLG	1N5939B
1N5817G	1N5832	1N5926B	1N5940B
1N5817RLG	1N5833	1N5927B	1N5940BRLG
1N5818G	1N5834	1N5927BG	1N5941B
1N5818RLG	1N5913B	1N5927BRLG	1N5941BRLG
1N5819G	1N5913BRLG	1N5928B	1N5942B
1N5819RLG	1N5914B	1N5929B	1N5942BRLG
1N5820	1N5915B	1N5929BG	1N5943B
1N5820G	1N5916B	1N5929BRLG	1N5944B
1N5820RLG	1N5917B	1N5930B	1N5945B
1N5821	1N5918B	1N5931B	1N5946B

Multisim 14.0 Full Components

1N5946BRLG	1N6002B	1N6098	1N756A
1N5947B	1N6003B	1N6285AG	1N757A
1N5948BRLG	1N6004B	1N6285ARL4G	1N758A
1N5953BG	1N6005B	1N6287AG	1N759A
1N5953BRLG	1N6006B	1N6287ARL4G	1N914
1N5955BRLG	1N6007B	1N6292AG	1N914A
1N5956BG	1N6008B	1N6292ARL4G	1N914B
1N5956BRLG	1N6009B	1N6294ARL4G	1N916
1N5985B	1N6010B	1N6373-E3/51	1N916A
1N5986B	1N6011B	1N6478	1N916B
1N5987B	1N6012B	1N6479	1N957B
1N5988B	1N6013B	1N6480	1N958B
1N5989B	1N6014B	1N6481	1N959B
1N5990B	1N6015B	1N6482	1N960B
1N5991B	1N6016B	1N6483	1N961B
1N5992B	1N6017B	1N6484	1N962B
1N5993B	1N6018B	1N747A	1N963B
1N5994B	1N6019B	1N748A	1N964B
1N5995B	1N6020B	1N749A	1N965B
1N5996B	1N6021B	1N750A	1N966B
1N5997B	1N6022B	1N751A	1N967B
1N5998B	1N6023B	1N752A	1N968B
1N5999B	1N6024B	1N753A	1N969B
1N6000B	1N6025B	1N754A	1N970B
1N6001B	1N6096	1N755A	1N971B

Multisim 14.0 Full Components

1N972B	1PMT16AT3G	1PS76SB10	1SMA26AT3G
1N973B	1PMT33AT3G	1PS76SB17	1SMA30AT3G
1N974B	1PMT5.0AT1G	1PS76SB40	1SMA40CAT3G
1N975B	1PMT5927BT1G	1PS76SB70	1SMA5.0AT3G
1N976B	1PS10SB82	1PS79SB10	1SMA5913BT3G
1N977B	1PS300	1PS79SB17	1SMA5918BT3G
1N978B	1PS301	1PS79SB30	1SMA5921BT3G
1N979B	1PS302	1PS79SB31	1SMA5922BT3G
1N980B	1PS66SB17	1PS79SB40	1SMA5927BT3G
1N981B	1PS66SB82	1PS79SB70	1SMA5931BT3G
1N982B	1PS70SB10	1PS88SB48	1SMA5932BT3G
1N983B	1PS70SB14	1PS88SB82	1SMA5936BT3G
1N984B	1PS70SB15	1S1553	1SMA5940BT3G
1N985B	1PS70SB16	1S1554	1SMB12AT3G
1N986B	1PS70SB20	1S1555	1SMB14AT3G
1N987B	1PS70SB40	1S1830	1SMB170AT3G
1N988B	1PS70SB44	1S1834	1SMB18CAT3G
1N989B	1PS70SB45	1S1835	1SMB20CAT3G
1N990B	1PS70SB46	1S1885	1SMB22CAT3G
1N991B	1PS70SB82	1S1887	1SMB24AT3G
1N992B	1PS70SB84	1S1888	1SMB24CAT3G
1P1S	1PS70SB85	1S953	1SMB26CAT3G
1P2S	1PS70SB86	1S954	1SMB28AT3G
1P3S	1PS74SB23	1S955	1SMB28CAT3G
1PMT12AT1G	1PS75SB45	1SMA12CAT3G	1SMB30AT3G

Multisim 14.0 Full Components

1SMB30CAT3G	1SMB85AT3G	1ZB8.2	2.2 nF [C0402C222K5RACT U]
1SMB33CAT3G	1SMC28AT3G	1ZB9.1	
1SMB36CAT3G	1SMC36AT3G	2 nF [C0603C202K1HACT U]	2.2 nF [C0402C222K8RACT U]
1SMB5.0AT3G	1SMC6.0AT3G		
1SMB54CAT3G	1Z10	2 nF [C0603C202K3HACT U]	2.2 nF [C0603C222K1HACT U]
1SMB58CAT3G	1Z11		
1SMB5914BT3G	1Z12	2 nF [C0603C202K5HACT U]	2.2 nF [C0603C222K1RACT U]
1SMB5918BT3G	1Z13		
1SMB5919BT3G	1Z14	2 nF [C1210C202KCGAC TU]	2.2 nF [C0603C222K2RACT U]
1SMB5920BT3G	1Z15		
1SMB5921BT3G	1Z30	2 nF [C1812C202KBGAC TU]	2.2 nF [C0603C222K3GACT U]
1SMB5922BT3G	1Z6.2		
1SMB5924BT3G	1Z6.8	2 nF [C1825C202KBGAC TU]	2.2 nF [C0603C222K3HACT U]
1SMB5925BT3G	1Z7.5		
1SMB5927BT3G	1Z8.2	2 nF [C2220C202KBGAC TU]	2.2 nF [C0603C222K3RACT U]
1SMB5930BT3G	1Z9.1		
1SMB5931BT3G	1ZB10	2 nF [C2225C202KBGAC TU]	2.2 nF [C0603C222K4RACT U]
1SMB5933BT3G	1ZB11		
1SMB5934BT3G	1ZB12	2.2 nF [C0402C222K3RACT U]	2.2 nF [C0603C222K5HACT U]
1SMB5935BT3G	1ZB13		
1SMB5936BT3G	1ZB14	2.2 nF [C0402C222K4RACT U]	2.2 nF [C0603C222K5RACT U]
1SMB5937BT3G	1ZB15		
1SMB5939BT3G	1ZB30		
1SMB5940BT3G	1ZB6.8	2.2 nF [C0402C222K4RACT U]	2.2 nF [C0603C222K5RACT U]
1SMB70AT3G	1ZB7.5		

Multisim 14.0 Full Components

2.2 nF [C0603C222K8RACT U]	2.2 nF [C0805C222KARACT U]	2.2 nF [C1210C222KCGAC TU]	2.2 uF [C0603C225K4PACT U]
2.2 nF [C0603C222K9RACT U]	2.2 nF [C1206C222K1GACT U]	2.2 nF [C1812C222K2GACT U]	2.2 uF [C0603C225K8PACT U]
2.2 nF [C0805C222K1GACT U]	2.2 nF [C1206C222K1RACT U]	2.2 nF [C1812C222KBGAC TU]	2.2 uF [C0603C225K9PACT U]
2.2 nF [C0805C222K1HACT U]	2.2 nF [C1206C222K2RACT U]	2.2 nF [C1812C222KDGAC TU]	2.2 uF [C0805C225K4PACT U]
2.2 nF [C0805C222K1RACT U]	2.2 nF [C1206C222K4RACT U]	2.2 nF [C1825C222KBGAC TU]	2.2 uF [C0805C225K4RACT U]
2.2 nF [C0805C222K2RACT U]	2.2 nF [C1206C222K5GACT U]	2.2 nF [C2220C222KBGAC TU]	2.2 uF [C0805C225K8PACT U]
2.2 nF [C0805C222K3GACT U]	2.2 nF [C1206C222K5RACT U]	2.2 nF [C2225C222KBGAC TU]	2.2 uF [C0805C225K8RACT U]
2.2 nF [C0805C222K3HACT U]	2.2 nF [C1210C222K1GACT U]	2.2 nF [CA064C222K1RACT U]	2.2 uF [C0805C225K9PACT U]
2.2 nF [C0805C222K3RACT U]	2.2 nF [C1210C222K1RACT U]	2.2 nF [CA064C222K4RACT U]	2.2 uF [C0805C225K9RACT U]
2.2 nF [C0805C222K5HACT U]	2.2 nF [C1210C222K2GACT U]	2.2 nF [CA064C222K5RACT U]	2.2 uF [C0805C225M4VAC TU]
2.2 nF [C0805C222K5RACT U]	2.2 nF [C1210C222K5GACT U]	2.2 uF [C0402C225K9PACT U]	2.2 uF [C0805C225M8VAC TU]

Multisim 14.0 Full Components

2.2 uF [C1206C225K3NAC TU]	2.2 uF [C1210C225K3RACT U]	2.2 uF [C2225C225M5UAC TU]	2.2 uF [T491C225M035AT]
2.2 uF [C1206C225K3PACT U]	2.2 uF [C1210C225K4RACT U]	2.2 uF [T409C225M015AH 4250]	2.2 uF [T491C225M050AT]
2.2 uF [C1206C225K4PACT U]	2.2 uF [C1210C225K5RACT U]	2.2 uF [T429A225M010AH 4250]	2.2 uF [T491D225M050AT]
2.2 uF [C1206C225K4RACT U]	2.2 uF [C1210C225K8RACT U]	2.2 uF [T429C225M015AH 4250]	2.2 uF [T491S225M016AT]
2.2 uF [C1206C225K8PACT U]	2.2 uF [C1210C225K9PACT U]	2.2 uF [T491A225M006AT]	2.2 uF [T494A225M010AT]
2.2 uF [C1206C225K8RACT U]	2.2 uF [C1210C225K9RACT U]	2.2 uF [T491A225M010AT]	2.2 uF [T494A225M016AT]
2.2 uF [C1206C225K9PACT U]	2.2 uF [C1210C225M8VAC TU]	2.2 uF [T491A225M016AT]	2.2 uF [T494A225M020AT]
2.2 uF [C1206C225K9RACT U]	2.2 uF [C1812C225K1RACT U]	2.2 uF [T491A225M020AT]	2.2 uF [T494B225M020AT]
2.2 uF [C1206C225M4VAC TU]	2.2 uF [C1825C225K5RACT U]	2.2 uF [T491A225M025AT]	2.2 uF [T494B225M025AT]
2.2 uF [C1210C225K1RACT U]	2.2 uF [C2220C225K5RACT U]	2.2 uF [T491B225M010AT]	2.2 uF [T494B225M035AT]
2.2 uF [C1210C225K3PACT U]	2.2 uF [C2225C225K5RACT U]	2.2 uF [T491B225M020AT]	2.2 uF [T494C225M025AT]
		2.2 uF [T491B225M025AT]	2.2 uF [T494C225M035AT]
		2.2 uF [T491B225M035AT]	2.2 uF [T494C225M050AT]
		2.2 uF [T491C225M025AT]	2.2 uF [T494D225M050AT]

Multisim 14.0 Full Components

2.2 uF [T494S225M016AT]	2.4 nF [C2220C242KBGAC TU]	2.7 nF [C0603C272K5HACT U]	2.7 nF [C0805C272K4RACT U]
2.2 uF [T498A225M010AT E4K6]	2.4 nF [C2225C242KBGAC TU]	2.7 nF [C0603C272K5RACT U]	2.7 nF [C0805C272K5HACT U]
2.2 uF [T498B225M025AT E3K0]	2.7 nF [C0402C272K3RACT U]	2.7 nF [C0603C272K8RACT U]	2.7 nF [C0805C272K5RACT U]
2.4 nF [C0603C242K1HACT U]	2.7 nF [C0402C272K4RACT U]	2.7 nF [C0805C272K1GACT U]	2.7 nF [C0805C272KARACT U]
2.4 nF [C0603C242K3HACT U]	2.7 nF [C0402C272K5RACT U]	2.7 nF [C0805C272K1HACT U]	2.7 nF [C1206C272K1GACT U]
2.4 nF [C0603C242K5HACT U]	2.7 nF [C0603C272K1HACT U]	2.7 nF [C0805C272K1RACT U]	2.7 nF [C1206C272K1RACT U]
2.4 nF [C0805C242K1GACT U]	2.7 nF [C0603C272K1RACT U]	2.7 nF [C0805C272K2RACT U]	2.7 nF [C1206C272K2RACT U]
2.4 nF [C0805C242K1HACT U]	2.7 nF [C0603C272K3GACT U]	2.7 nF [C0805C272K3GACT U]	2.7 nF [C1206C272K5GACT U]
2.4 nF [C0805C242K3HACT U]	2.7 nF [C0603C272K3HACT U]	2.7 nF [C0805C272K3HACT U]	2.7 nF [C1206C272K5RACT U]
2.4 nF [C0805C242K5HACT U]	2.7 nF [C0603C272K3RACT U]	2.7 nF [C0805C272K3RACT U]	2.7 nF [C1210C272K2GACT U]
2.4 nF [C1825C242KBGAC TU]	2.7 nF [C0603C272K4RACT U]	2.7 nF [C0805C272K4GACT U]	2.7 nF [C1210C272K5GACT U]

Multisim 14.0 Full Components

2.7 nF [C1210C272KCGAC TU]	2.7 uF [C1206C275K9PACT U]	20 pF [C1206C200K1GACT U]	200 pF [C0402C201K5HACT U]
2.7 nF [C1812C272K1GACT U]	2.7 uF [C1206C275K9RACT U]	20 pF [C1206C200K5GACT U]	200 pF [C0603C201K5GACT U]
2.7 nF [C1812C272K5GACT U]	2 AMP 20 pF [C0402C200K5GACT U]	20 pF [C1206C200KBGAC TU]	200 pF [C0805C201K2GACT U]
2.7 nF [C1825C272KBGAC TU]	20 pF [C0402C200K8GACT U]	20 pF [C1206C200KCGAC TU]	200 pF [C0805C201K5GACT U]
2.7 nF [C2220C272KBGAC TU]	20 pF [C0603C200K2GACT U]	20 pF [C1210C200KBGAC TU]	200 pF [C1206C201K5GACT U]
2.7 nF [C2225C272KBGAC TU]	20 pF [C0603C200K4GACT U]	20 pF [C1812C200KBGAC TU]	200 pF [C1206C201KBGAC TU]
2.7 uF [C0805C275K8PACT U]	20 pF [C0603C200K5GACT U]	20 pF [C1825C200KBGAC TU]	200 pF [C1210C201KBGAC TU]
2.7 uF [C1206C275K3PACT U]	20 pF [C0805C200K1GACT U]	20 pF [C2220C200KBGAC TU]	200 pF [C1812C201KBGAC TU]
2.7 uF [C1206C275K4PACT U]	20 pF [C0805C200K2GACT U]	20 pF [C2225C200KBGAC TU]	200 pF [C2220C201KBGAC TU]
2.7 uF [C1206C275K4RACT U]	20 pF [C0805C200K5GACT U]	20 AMP 200 pF [C0402C201K1HACT U]	200 pF [C2225C201KBGAC TU]
2.7 uF [C1206C275K8RACT U]	20 pF [C0805C200KBGAC TU]	200 pF [C0402C201K3HACT U]	2013655-1 22 nF [C0402C223K3RACT U]

Multisim 14.0 Full Components

22 nF [C0402C223K4RACT U]	22 nF [C0603C223M3VAC TU]	22 nF [C0805C223KARACT U]	22 nF [C1206C223K3RACT U]
22 nF [C0402C223K5RACT U]	22 nF [C0603C223M8VAC TU]	22 nF [C0805C223M5UAC TU]	22 nF [C1206C223K4RACT U]
22 nF [C0402C223K8PACT U]	22 nF [C0805C223K1RACT U]	22 nF [C0805F223K1RACT U]	22 nF [C1206C223K5HACT U]
22 nF [C0402C223K8RACT U]	22 nF [C0805C223K2RACT U]	22 nF [C0805F223K3RACT U]	22 nF [C1206C223K5RACT U]
22 nF [C0402C223K9PACT U]	22 nF [C0805C223K3GACT U]	22 nF [C0805F223K4RACT U]	22 nF [C1206C223M5UAC TU]
22 nF [C0402C223K9RACT U]	22 nF [C0805C223K3HACT U]	22 nF [C0805F223K5RACT U]	22 nF [C1206F223K2RACT U]
22 nF [C0603C223K1RACT U]	22 nF [C0805C223K3RACT U]	22 nF [C1206C223K1HACT U]	22 nF [C1210C223K1GACT U]
22 nF [C0603C223K3RACT U]	22 nF [C0805C223K4RACT U]	22 nF [C1206C223K1RACT U]	22 nF [C1210C223K1HACT U]
22 nF [C0603C223K4RACT U]	22 nF [C0805C223K5HACT U]	22 nF [C1206C223K2RACT U]	22 nF [C1210C223K1RACT U]
22 nF [C0603C223K5RACT U]	22 nF [C0805C223K5RACT U]	22 nF [C1206C223K3GACT U]	22 nF [C1210C223K2RACT U]
22 nF [C0603C223K8RACT U]	22 nF [C0805C223K8RACT U]	22 nF [C1206C223K3HACT U]	22 nF [C1210C223K3GACT U]

Multisim 14.0 Full Components

22 nF [C1210C223K3HACT U]	22 nF [C1812C223K5RACT U]	22 pF [C0402C220K5GACT U]	22 pF [C0805C220KBGAC TU]
22 nF [C1210C223K5GACT U]	22 nF [C1825C223K1GACT U]	22 pF [C0402C220K8GACT U]	22 pF [C0805C220KCGAC TU]
22 nF [C1210C223K5HACT U]	22 nF [C1825C223K5GACT U]	22 pF [C0603C220K1GACT U]	22 pF [C0805C220KDGAC TU]
22 nF [C1210C223K5RACT U]	22 nF [C1825C223K5RACT U]	22 pF [C0603C220K2GACT U]	22 pF [C1206C220K1GACT U]
22 nF [C1210C223KARACT U]	22 nF [C2220C223K1GACT U]	22 pF [C0603C220K3GACT U]	22 pF [C1206C220K2GACT U]
22 nF [C1812C223K1GACT U]	22 nF [C2220C223K2GACT U]	22 pF [C0603C220K4GACT U]	22 pF [C1206C220K5GACT U]
22 nF [C1812C223K1HACT U]	22 nF [C2225C223K1GACT U]	22 pF [C0603C220K5GACT U]	22 pF [C1206C220KBGAC TU]
22 nF [C1812C223K1RACT U]	22 nF [C2225C223K5GACT U]	22 pF [C0805C220K1GACT U]	22 pF [C1206C220KCGAC TU]
22 nF [C1812C223K2RACT U]	22 pF [C0201C220K3GACT U]	22 pF [C0805C220K2GACT U]	22 pF [C1206C220KDGAC TU]
22 nF [C1812C223K5GACT U]	22 pF [C0402C220K3GACT U]	22 pF [C0805C220K3GACT U]	22 pF [C1210C220K2GACT U]
22 nF [C1812C223K5HACT U]	22 pF [C0402C220K4GACT U]	22 pF [C0805C220K5GACT U]	22 pF [C1210C220K5GACT U]

Multisim 14.0 Full Components

22 pF [C1210C220KBGAC TU]	22 uF [A700V226M006AT E028]	22 uF [C1210C226K8RACT U]	22 uF [T491B226M020AT]
22 pF [C1812C220KBGAC TU]	22 uF [A700V226M006AT E045]	22 uF [C1210C226K9PACT U]	22 uF [T491C226M004AT]
22 pF [C1825C220KBGAC TU]	22 uF [A700V226M008AT E028]	22 uF [C1210C226K9RACT U]	22 uF [T491C226M006AT]
22 pF [C2220C220KBGAC TU]	22 uF [A700V226M008AT E045]	22 uF [C1210C226M8VAC TU]	22 uF [T491C226M010AT]
22 pF [C2225C220KBGAC TU]	22 uF [A700V226M010AT E028]	22 uF [T419G226M020AH 4250]	22 uF [T491C226M016AT]
22 pF [CA064C220K2GAC TU]	22 uF [A700V226M12RAT E030]	22 uF [T429D226M006AH 4250]	22 uF [T491C226M020AT]
22 pF [CA064C220K3GAC TU]	22 uF [C0805C226K9PACT U]	22 uF [T491A226M004AT]	22 uF [T491D226M010AT]
22 pF [CA064C220K4GAC TU]	22 uF [C1206C226K9PACT U]	22 uF [T491A226M006AT]	22 uF [T491D226M016AT]
22 pF [CA064C220K5GAC TU]	22 uF [C1206C226K9PACT U]	22 uF [T491A226M010AT]	22 uF [T491D226M020AT]
22 pF [CA064C220K5GAC TU]	22 uF [C1206C226M9VAC TU]	22 uF [T491B226M004AT]	22 uF [T491D226M025AT]
22 pF [CA064C220K8GAC TU]	22 uF [C1210C226K4PACT U]	22 uF [T491B226M006AT]	22 uF [T491D226M025AT]
22 uF [A700D226M016AT E018]	22 uF [C1210C226K8PACT U]	22 uF [T491B226M010AT]	22 uF [T491D226M035AT]
		22 uF [T491B226M016AT]	22 uF [T491S226M004AT]

Multisim 14.0 Full Components

22 uF [T491T226M004AT]	22 uF [T494B226M004AT]	22 uF [T494D226M025AT]	22 uF [T495C226M025AT E300]
22 uF [T491T226M006AT]	22 uF [T494B226M006AT]	22 uF [T494D226M035AT]	22 uF [T495C226M025AT E900]
22 uF [T491T226M010AT]	22 uF [T494B226M010AT]	22 uF [T494S226M004AT]	22 uF [T495D226M020AT E180]
22 uF [T491U226M006AT]	22 uF [T494B226M016AT]	22 uF [T494T226M004AT]	22 uF [T495D226M020AT E225]
22 uF [T491U226M010AT]	22 uF [T494C226M004AT]	22 uF [T494T226M006AT]	22 uF [T495D226M025AT E200]
22 uF [T491U226M016AT]	22 uF [T494C226M006AT]	22 uF [T494T226M010AT]	22 uF [T495D226M035AT E125]
22 uF [T491V226M020AT]	22 uF [T494C226M010AT]	22 uF [T494U226M006AT]	22 uF [T495D226M035AT E200]
22 uF [T491V226M025AT]	22 uF [T494C226M016AT]	22 uF [T494U226M010AT]	22 uF [T495D226M035AT E300]
22 uF [T491X226M035AT]	22 uF [T494C226M020AT]	22 uF [T494U226M016AT]	22 uF [T495X226M025AT E225]
22 uF [T491X226M050AT]	22 uF [T494C226M025AT]	22 uF [T494V226M020AT]	22 uF [T495X226M035AT E125]
22 uF [T493X226M025AH 6110]	22 uF [T494D226M010AT]	22 uF [T494V226M025AT]	22 uF [T495X226M035AT E200]
22 uF [T494A226M004AT]	22 uF [T494D226M016AT]	22 uF [T494X226M035AT]	
22 uF [T494A226M006AT]	22 uF [T494D226M020AT]		
22 uF [T494A226M010AT]			

Multisim 14.0 Full Components

22 uF [T495X226M035AT E275]	22 uF [T510X226M035AT E100]	220 nF [C0402C224K9PACT U]	220 nF [C0805C224K5RACT U]
22 uF [T497D226M006AT 6110]	22 uF [T520A226M006AT E090]	220 nF [C0603C224K3RACT U]	220 nF [C0805C224K8RACT U]
22 uF [T498B226M010AT E1K5]	22 uF [T520A226M006AT E100]	220 nF [C0603C224K4RACT U]	220 nF [C0805C224M3VAC TU]
22 uF [T498C226M006AT E1K3]	22 uF [T520A226M010AT E080]	220 nF [C0603C224K8NAC TU]	220 nF [C0805C224M4VAC TU]
22 uF [T498C226M010AT E1K1]	22 uF [T520C226M016AT E080]	220 nF [C0603C224K8RACT U]	220 nF [C1206C224K1RACT U]
22 uF [T498C226M016AT E1K0]	22 uF [T520T226M008AT E070]	220 nF [C0603C224K9RACT U]	220 nF [C1206C224K3RACT U]
22 uF [T498D226M025AT E600]	22 uF [T520V226M020AT E045]	220 nF [C0603C224M3VAC TU]	220 nF [C1206C224K4RACT U]
22 uF [T498X226M035AT E500]	22 uF [T520V226M020AT E090]	220 nF [C0603C224M4VAC TU]	220 nF [C1206C224K5RACT U]
22 uF [T499D226M016AT E800]	22 uF [T521V226M025AT E060]	220 nF [C0603C224M8VAC TU]	220 nF [C1206C224M5UAC TU]
22 uF [T510X226M035AT E060]	22 uF [T525B226M010AT E080]	220 nF [C0805C224K3RACT U]	220 nF [C1206F224K3RACT U]
22 uF [T510X226M035AT E080]	22 uF [T541X226M050AH 6510]	220 nF [C0805C224K4RACT U]	220 nF [C1206F224K4RACT U]

Multisim 14.0 Full Components

220 nF [C1206F224K5RACT U]	220 nF [C1812C224K5HACT U]	220 nF [C1825C224M1UAC TU]	220 nF [T499A224M035AT E18K]
220 nF [C1210C224K1RACT U]	220 nF [C1812C224K5RACT U]	220 nF [C1825C224M5UAC TU]	220 pF [C0402C221K1HACT U]
220 nF [C1210C224K3GACT U]	220 nF [C1812C224KARACT U]	220 nF [C2220C224K1GACT U]	220 pF [C0402C221K3HACT U]
220 nF [C1210C224K3RACT U]	220 nF [C1812C224M5UAC TU]	220 nF [C2220C224K5GACT U]	220 pF [C0402C221K3RACT U]
220 nF [C1210C224K5RACT U]	220 nF [C1812F224K1RACT U]	220 nF [C2225C224K1RACT U]	220 pF [C0402C221K4RACT U]
220 nF [C1210C224M5UAC TU]	220 nF [C1812F224K2RACT U]	220 nF [C2225C224K5RACT U]	220 pF [C0402C221K5GACT U]
220 nF [C1210F224K1RACT U]	220 nF [C1812F224K3RACT U]	220 nF [T409A224M035AH 4250]	220 pF [C0402C221K5HACT U]
220 nF [C1210F224K3RACT U]	220 nF [C1812F224K5RACT U]	220 nF [T491A224M035AT]	220 pF [C0402C221K5RACT U]
220 nF [C1210F224K4RACT U]	220 nF [C1825C224K1RACT U]	220 nF [T491B224M050AT]	220 pF [C0402C221K8RACT U]
220 nF [C1210F224K5RACT U]	220 nF [C1825C224K2RACT U]	220 nF [T493B224M050AH 6120]	220 pF [C0603C221K1RACT U]
220 nF [C1812C224K1RACT U]	220 nF [C1825C224K5RACT U]	220 nF [T494A224M035AT]	220 pF [C0603C221K2RACT U]

Multisim 14.0 Full Components

220 pF [C0603C221K3GACT U]	220 pF [C0805C221K3GACT U]	220 pF [C1206C221KCGAC TU]	220 uF [A700D227M002AT E018]
220 pF [C0603C221K3RACT U]	220 pF [C0805C221K3RACT U]	220 pF [C1206C221KDGAC TU]	220 uF [A700D227M004AT E009]
220 pF [C0603C221K4GACT U]	220 pF [C0805C221K4RACT U]	220 pF [C1210C221K1GACT U]	220 uF [A700V227M002AT E009]
220 pF [C0603C221K4RACT U]	220 pF [C0805C221K5GACT U]	220 pF [C1210C221KBGAC TU]	220 uF [A700X227M004AT E010]
220 pF [C0603C221K5GACT U]	220 pF [C0805C221K5RACT U]	220 pF [C1812C221KBGAC TU]	220 uF [A700X227M004AT E015]
220 pF [C0603C221K5RACT U]	220 pF [C0805C221K8RACT U]	220 pF [C1825C221KBGAC TU]	220 uF [A700X227M2R5AT E010]
220 pF [C0603C221K8RACT U]	220 pF [C0805C221KARACT U]	220 pF [C2220C221KBGAC TU]	220 uF [A700X227M2R5AT E015]
220 pF [C0805C221K1GACT U]	220 pF [C1206C221K1GACT U]	220 pF [C2225C221KBGAC TU]	220 uF [T419H227M004AH 4250]
220 pF [C0805C221K1RACT U]	220 pF [C1206C221K2GACT U]	220 pF [CA064C221K5GAC TU]	220 uF [T491B227M004AT]
220 pF [C0805C221K2GACT U]	220 pF [C1206C221K5GACT U]	220 pF [CDR02BP221BKSM]	220 uF [T491C227M006AT]
220 pF [C0805C221K2RACT U]	220 pF [C1206C221KBGAC TU]	220 uF [A700D227M002AT E015]	220 uF [T491D227M006AT]
			220 uF [T491D227M010AT]

Multisim 14.0 Full Components

220 uF [T491D227M2R5AT]	220 uF [T494V227M006AT]	220 uF [T495D227M010AT E100]	220 uF [T495X227M010AT E100]
220 uF [T491E227M016AT]	220 uF [T494X227M006AT]	220 uF [T495D227M010AT E125]	220 uF [T495X227M016AT E100]
220 uF [T491V227M004AT]	220 uF [T494X227M010AT]	220 uF [T495D227M2R5AT E045]	220 uF [T496X227M010AT 6110]
220 uF [T491V227M006AT]	220 uF [T494X227M016AT]	220 uF [T495D227M016AT E045]	220 uF [T496X227M010AT 6110]
220 uF [T491X227M006AT]	220 uF [T495C227M006AT E225]	220 uF [T495E227M016AT E050]	220 uF [T498X227M010AT E500]
220 uF [T491X227M010AT]	220 uF [T495D227M004AT E040]	220 uF [T495E227M016AT E075]	220 uF [T510X227M016AT E025]
220 uF [T491X227M016AT]	220 uF [T495D227M004AT E050]	220 uF [T495E227M016AT E150]	220 uF [T510X227M016AT E040]
220 uF [T494B227M004AT]	220 uF [T495D227M004AT E050]	220 uF [T495E227M016AT E150]	220 uF [T510X227M016AT E040]
220 uF [T494C227M006AT]	220 uF [T495D227M004AT E100]	220 uF [T495X227M006AT E100]	220 uF [T513X227M016AH 6110]
220 uF [T494D227M006AT]	220 uF [T495D227M006AT E045]	220 uF [T495X227M010AT E045]	220 uF [T513X227M016AH 6120]
220 uF [T494D227M010AT]	220 uF [T495D227M006AT E100]	220 uF [T495X227M010AT E050]	220 uF [T520B227M004AT E035]
220 uF [T494D227M2R5AT]	220 uF [T495D227M010AT E045]	220 uF [T495X227M010AT E060]	220 uF [T520B227M004AT E045]
220 uF [T494E227M016AT]	220 uF [T495D227M010AT E075]	220 uF [T495X227M010AT E070]	220 uF [T520B227M004AT E070]
220 uF [T494V227M004AT]			

Multisim 14.0 Full Components

220 uF [T520B227M006AT E035]	220 uF [T520C227M006AT E025]	220 uF [T520D227M010AT E018]	220 uF [T520V227M004AT E018]
220 uF [T520B227M2R5AT E015]	220 uF [T520C227M006AT E045]	220 uF [T520D227M010AT E025]	220 uF [T520V227M004AT E025]
220 uF [T520B227M2R5AT E018]	220 uF [T520C227M2R5AT E025]	220 uF [T520D227M010AT E040]	220 uF [T520V227M004AT E040]
220 uF [T520B227M2R5AT E025]	220 uF [T520D227M004AT E012]	220 uF [T520D227M2R5AT E007]	220 uF [T520V227M004AT E045]
220 uF [T520B227M2R5AT E030]	220 uF [T520D227M004AT E065]	220 uF [T520D227M2R5AT E040]	220 uF [T520V227M006AT E007]
220 uF [T520B227M2R5AT E035]	220 uF [T520D227M006AT E006]	220 uF [T520U227M2R5AT E055]	220 uF [T520V227M006AT E009]
220 uF [T520B227M2R5AT E070]	220 uF [T520D227M006AT E007]	220 uF [T520V227M004AT E006]	220 uF [T520V227M006AT E012]
220 uF [T520C227M004AT E018]	220 uF [T520D227M006AT E009]	220 uF [T520V227M004AT E007]	220 uF [T520V227M006AT E015]
220 uF [T520C227M004AT E025]	220 uF [T520D227M006AT E015]	220 uF [T520V227M004AT E009]	220 uF [T520V227M006AT E018]
220 uF [T520C227M004AT E045]	220 uF [T520D227M006AT E040]	220 uF [T520V227M004AT E012]	220 uF [T520V227M006AT E025]
220 uF [T520C227M004AT E055]	220 uF [T520D227M006AT E050]	220 uF [T520V227M004AT E015]	220 uF [T520V227M006AT E040]

Multisim 14.0 Full Components

220 uF [T520V227M010AT E045]	220 uF [T522V227M006AT E040]	220 uF [T530D227M010AT E006]	24 pF [C1210C240KBGAC TU]
220 uF [T520V227M2R5AT E007]	220 uF [T525D227M004AT E025]	220 uF [T530D227M010AT E010]	24 pF [C1812C240KBGAC TU]
220 uF [T520V227M2R5AT E009]	220 uF [T525D227M006AT E025]	220 uF [T530Y227M010AT E006]	24 pF [C1825C240KBGAC TU]
220 uF [T520V227M2R5AT E012]	220 uF [T525D227M010AT E025]	220 uF [T541D227M010AH 6510]	24 pF [C1825C240KCGAC TU]
220 uF [T520V227M2R5AT E015]	220 uF [T528Z227M004AT E007]	220 uF [T543V227M004AT E015]	24 pF [C2220C240KBGAC TU]
220 uF [T520V227M2R5AT E025]	220 uF [T528Z227M004AT E009]	24 pF [C0402C240K4GACT U]	24 pF [C2225C240KBGAC TU]
220 uF [T520V227M2R5AT E045]	220 uF [T528Z227M004AT E012]	24 pF [C0402C240K5GACT U]	240 pF [C0402C241K1HACT U]
220 uF [T520W227M004AT E025]	220 uF [T528Z227M006AT E009]	24 pF [C0603C240K2GACT U]	240 pF [C0402C241K3HACT U]
220 uF [T520W227M004AT E040]	220 uF [T528Z227M006AT E012]	24 pF [C0805C240K5GACT U]	240 pF [C0402C241K5HACT U]
220 uF [T520Y227M010AT E040]	220 uF [T530D227M006AT E005]	24 pF [C0805C240KBGAC TU]	240 pF [C0603C241K5GACT U]
220 uF [T522V227M006AT E025]	220 uF [T530D227M006AT E006]	24 pF [C1206C240KBGAC TU]	240 pF [C0805C241K5GACT U]

Multisim 14.0 Full Components

240 pF [C1206C241KBGAC TU]	27 nF [C0402C273K8PACT U]	27 nF [C0805C273K3RACT U]	27 nF [C1206C273K3HACT U]
240 pF [C1210C241KBGAC TU]	27 nF [C0402C273K8RACT U]	27 nF [C0805C273K4RACT U]	27 nF [C1206C273K5HACT U]
240 pF [C1812C241KBGAC TU]	27 nF [C0402C273K9PACT U]	27 nF [C0805C273K5RACT U]	27 nF [C1206C273K5RACT U]
240 pF [C1825C241KBGAC TU]	27 nF [C0402C273K9RACT U]	27 nF [C0805C273K8RACT U]	27 nF [C1206C273KARACT U]
240 pF [C2220C241KBGAC TU]	27 nF [C0603C273K1RACT U]	27 nF [C0805C273M5UAC TU]	27 nF [C1210C273K1GACT U]
240 pF [C2225C241KBGAC TU]	27 nF [C0603C273K3RACT U]	27 nF [C0805F273K1RACT U]	27 nF [C1210C273K1HACT U]
25_AMP 2-534206-0	27 nF [C0603C273K4RACT U]	27 nF [C0805F273K3RACT U]	27 nF [C1210C273K1RACT U]
27 mF [C0402C279K5GACT U]	27 nF [C0603C273K5RACT U]	27 nF [C0805F273K4RACT U]	27 nF [C1210C273K2RACT U]
27 mF [C0805C279KBGAC TU]	27 nF [C0805C273K1RACT U]	27 nF [C0805F273K5RACT U]	27 nF [C1210C273K3GACT U]
27 nF [C0402C273K3RACT U]	27 nF [C0805C273K2RACT U]	27 nF [C1206C273K1HACT U]	27 nF [C1210C273K3HACT U]
27 nF [C0402C273K4RACT U]	27 nF [C0805C273K3HACT U]	27 nF [C1206C273K1RACT U]	27 nF [C1210C273K5GACT U]

Multisim 14.0 Full Components

27 nF [C1210C273K5HACT U]	27 pF [C0402C270K3GACT U]	27 pF [C0805C270KDGAC TU]	27 pF [CA064C270K5GAC TU]
27 nF [C1210C273K5RACT U]	27 pF [C0402C270K4GACT U]	27 pF [C1206C270K1GACT U]	27 pF [CA064C270K8GAC TU]
27 nF [C1210C273KARACT U]	27 pF [C0402C270K5GACT U]	27 pF [C1206C270K2GACT U]	270 nF [C0603C274K4PACT U]
27 nF [C1812C273K1HACT U]	27 pF [C0402C270K8GACT U]	27 pF [C1206C270K5GACT U]	270 nF [C0603C274K4RACT U]
27 nF [C1812C273K1RACT U]	27 pF [C0603C270K1GACT U]	27 pF [C1206C270KBGAC TU]	270 nF [C0603C274K8PACT U]
27 nF [C1812C273K5HACT U]	27 pF [C0603C270K2GACT U]	27 pF [C1210C270KBGAC TU]	270 nF [C0603C274K8RACT U]
27 nF [C1825C273K1GACT U]	27 pF [C0603C270K5GACT U]	27 pF [C1812C270KBGAC TU]	270 nF [C0603C274K9PACT U]
27 nF [C1825C273K5GACT U]	27 pF [C0805C270K1GACT U]	27 pF [C1812C270KHGAC TU]	270 nF [C0603C274K9RACT U]
27 nF [C2220C273K1GACT U]	27 pF [C0805C270K2GACT U]	27 pF [C1825C270KBGAC TU]	270 nF [C0805C274K3RACT U]
27 nF [C2220C273K2GACT U]	27 pF [C0805C270K5GACT U]	27 pF [C2220C270KBGAC TU]	270 nF [C0805C274K4RACT U]
27 pF [C0201C270K3GACT U]	27 pF [C0805C270KBGAC TU]	27 pF [C2225C270KBGAC TU]	270 nF [C0805C274K8RACT U]

Multisim 14.0 Full Components

270 nF [C1206C274K1RACT U]	270 nF [C1210F274K1RACT U]	270 nF [C1825C274K1RACT U]	270 pF [C0402C271K4RACT U]
270 nF [C1206C274K3RACT U]	270 nF [C1210F274K3RACT U]	270 nF [C1825C274K5RACT U]	270 pF [C0402C271K5GACT U]
270 nF [C1206C274K4RACT U]	270 nF [C1210F274K4RACT U]	270 nF [C2220C274K1GACT U]	270 pF [C0402C271K5HACT U]
270 nF [C1206C274K5RACT U]	270 nF [C1210F274K5RACT U]	270 nF [C2220C274K5GACT U]	270 pF [C0402C271K5RACT U]
270 nF [C1206F274K3RACT U]	270 nF [C1812C274K1RACT U]	270 nF [C2220C274K5RACT U]	270 pF [C0402C271K8RACT U]
270 nF [C1206F274K4RACT U]	270 nF [C1812C274K5RACT U]	270 nF [C2225C274K1RACT U]	270 pF [C0603C271K1RACT U]
270 nF [C1206F274K5RACT U]	270 nF [C1812C274KARACT U]	270 nF [C2225C274K2RACT U]	270 pF [C0603C271K2RACT U]
270 nF [C1210C274K1RACT U]	270 nF [C1812F274K1RACT U]	270 nF [C2225C274K5RACT U]	270 pF [C0603C271K3RACT U]
270 nF [C1210C274K3RACT U]	270 nF [C1812F274K2RACT U]	270 pF [C0402C271K1HACT U]	270 pF [C0603C271K4GACT U]
270 nF [C1210C274K5RACT U]	270 nF [C1812F274K3RACT U]	270 pF [C0402C271K3HACT U]	270 pF [C0603C271K4RACT U]
270 nF [C1210C274M5UAC TU]	270 nF [C1812F274K5RACT U]	270 pF [C0402C271K3RACT U]	270 pF [C0603C271K5GACT U]

Multisim 14.0 Full Components

270 pF [C0603C271K5RACT U]	270 pF [C1206C271KBGAC TU]	27C128-15P	27C64E350-883
		27C128-17L	27C64Q200-883
270 pF [C0805C271K1GACT U]	270 pF [C1210C271KBGAC TU]	27C128-17P	27C64Q250-883
		27C128-20L	27C64Q350-883
270 pF [C0805C271K1RACT U]	270 pF [C1812C271KBGAC TU]	27C128-20P	282834-2
		27C128-25L	282834-4
270 pF [C0805C271K2GACT U]	270 pF [C1825C271KBGAC TU]	27C128-25P	282834-5
		27C256-12L	282834-8
270 pF [C0805C271K2RACT U]	270 pF [C2220C271KBGAC TU]	27C256-12P	28V_7.5W
		27C256-15L	292303-1
270 pF [C0805C271K4RACT U]	270 pF [C2225C271KBGAC TU]	27C256-15P	292304-1
		27C256-20L	2A3
270 pF [C0805C271K5GACT U]	270 uF [A700X277M002AT E010]	27C256-20P	2K8RAM
		27C64-12L	2N1599
270 pF [C0805C271K5RACT U]	270 uF [A700X277M002AT E015]	27C64-12P	2N2222A
		27C64-15L	2N2573
270 pF [C1206C271K1GACT U]	270 uF [A700X277M004AT E010]	27C64-15P	2N2574
		27C64-17L	2N2575
270 pF [C1206C271K2GACT U]	270 uF [A700X277M004AT E015]	27C64-17P	2N2576
		27C64-20L	2N2577
270 pF [C1206C271K5GACT U]	27C128-12L	27C64-20P	2N2578
	27C128-12P	27C64-25L	2N2579
	27C128-15L	27C64-25P	2N2608
		27C64E200-883	2N2609
		27C64E250-883	2N2712

Multisim 14.0 Full Components

2N2714	2N3685	2N3899	2N4091
2N2923	2N3686	2N3903	2N4092
2N2924	2N3687	2N3904	2N4093
2N2925	2N3702	2N3904G	2N4117A
2N3055A	2N3703	2N3905	2N4118A
2N3055AG	2N3707	2N3906	2N4119A
2N3055G	2N3711	2N3906G	2N4123
2N3370	2N3771G	2N3921	2N4124
2N3390	2N3772G	2N3922	2N4125
2N3391	2N3773G	2N3954	2N4126
2N3391A	2N3821	2N3954A	2N4167
2N3392	2N3822	2N3955	2N4168
2N3393	2N3823	2N3955A	2N4169
2N3394	2N3824	2N3956	2N4170
2N3414	2N3858A	2N3957	2N4171
2N3415	2N3859	2N3958	2N4172
2N3416	2N3859A	2N3966	2N4173
2N3417	2N3860	2N3967	2N4174
2N3442G	2N3870	2N3970	2N4183
2N3458	2N3871	2N3971	2N4184
2N3459	2N3872	2N3972	2N4185
2N3668	2N3873	2N4058	2N4186
2N3669	2N3896	2N4061	2N4187
2N3670	2N3897	2N4062	2N4188
2N3684	2N3898	2N4084	2N4189

Multisim 14.0 Full Components

2N4190	2N4400	2N4918G	2N5105
2N4199	2N4401	2N4919G	2N5114
2N4200	2N4402	2N4920G	2N5115
2N4201	2N4403	2N4921G	2N5116
2N4202	2N4409	2N4922G	2N5168
2N4203	2N4410	2N4923G	2N5169
2N4204	2N4416	2N5018	2N5170
2N4220	2N4416A	2N5019	2N5171
2N4220A	2N4424	2N5020	2N5172
2N4221	2N4441	2N5021	2N5191G
2N4221A	2N4442	2N5038G	2N5192G
2N4222	2N4443	2N5045	2N5194G
2N4222A	2N4444	2N5046	2N5195G
2N4223	2N4856	2N5047	2N5196
2N4286	2N4856A	2N5060	2N5197
2N4289	2N4857	2N5061	2N5199
2N4291	2N4857A	2N5062	2N5209
2N4338	2N4858	2N5063	2N5210
2N4339	2N4858A	2N5064	2N5223
2N4340	2N4859	2N5078	2N5224
2N4341	2N4859A	2N5086	2N5226
2N4381	2N4860	2N5087	2N5227
2N4391	2N4860A	2N5088	2N5232
2N4392	2N4861	2N5089	2N5232A
2N4393	2N4861A	2N5103	2N5302G

Multisim 14.0 Full Components

2N5354	2N5519	2N5769	2N6045G
2N5355	2N5520	2N5771	2N6052G
2N5358	2N5521	2N5817	2N6071
2N5365	2N5522	2N5830	2N6073BG
2N5366	2N5523	2N5883G	2N6107G
2N5397	2N5524	2N5884G	2N6109G
2N5398	2N5545	2N5885G	2N6111G
2N5400	2N5550	2N5886G	2N6145
2N5401	2N5550G	2N6027	2N6146
2N5432	2N5550RLRPG	2N6027G	2N6147
2N5433	2N5551	2N6027RL1G	2N6157
2N5434	2N5556	2N6027RLRAG	2N6158
2N5444	2N5557	2N6028	2N6159
2N5445	2N5558	2N6028G	2N6160
2N5446	2N5564	2N6028RLRAG	2N6161
2N5447	2N5565	2N6028RLRMG	2N6162
2N5452	2N5566	2N6028RLRPG	2N6163
2N5454	2N5567	2N6034G	2N6164
2N5484	2N5568	2N6035G	2N6165
2N5485	2N5571	2N6036G	2N6167
2N5486	2N5572	2N6038G	2N6168
2N5515	2N5655G	2N6039G	2N6169
2N5516	2N5657G	2N6040G	2N6170
2N5517	2N5684G	2N6042G	2N6171
2N5518	2N5686G	2N6043G	2N6172

Multisim 14.0 Full Components

2N6173	2N6400	2N7002DW	2PA1774SMB
2N6174	2N6401	2N7002E	2PB1219AQ
2N6284G	2N6402	2N7002ET1G	2PB1219AR
2N6286G	2N6403	2N7002F	2PB1219AS
2N6287G	2N6404	2N7002K	2PB1424
2N6288G	2N6405	2N7002LT1G	2PB709ARL
2N6292G	2N6487G	2N7002LT3G	2PB709ART
2N6338G	2N6488G	2N7002P	2PB709ARW
2N6341G	2N6490G	2N7002PS	2PB709ASL
2N6342	2N6491G	2N7002PT	2PB709ASW
2N6343	2N6667G	2N7002PV	2PB709BRL
2N6344	2N6715	2N7002PW	2PB709BSL
2N6345	2N6727	2P1S	2PB710ARL
2N6346	2N7000	2P2S	2PB710ASL
2N6347	2N7000G	2PA1576Q	2PC4081Q
2N6348	2N7000RLRAG	2PA1576R	2PC4081R
2N6349	2N7002	2PA1576S	2PC4081S
2N6387G	2N7002BK	2PA1774Q	2PC4617Q
2N6388G	2N7002BKM	2PA1774QM	2PC4617QM
2N6394	2N7002BKMB	2PA1774QMB	2PC4617QMB
2N6395	2N7002BKS	2PA1774R	2PC4617R
2N6396	2N7002BKT	2PA1774RM	2PC4617RM
2N6397	2N7002BKV	2PA1774RMB	2PC4617RMB
2N6398	2N7002BKW	2PA1774S	2PD1820AR
2N6399	2N7002CK	2PA1774SM	2PD1820AS

Multisim 14.0 Full Components

2PD2150	2SA2205-E	2SC5706-H	2SK117
2PD601ARL	2SA2205-TL-E	2SC5706-TL-E	2SK170
2PD601ART	2SA733	2SC5706-TL-H	2SK192A
2PD601ARW	2SA952	2SC5964-TD-E	2SK208
2PD601ASL	2SA953	2SC5964-TD-H	2SK209
2PD601ASW	2SA954	2SC945	2SK2553L
2PD601BRL	2SB1205S-TL-E	2SD1623S-TD-E	2SK2553S
2PD601BSL	2SB1205T-TL-E	2SD1623T-TD-E	2SK2978
2PD602AQL	2SC1815	2SD1628F-TD-E	2SK2980
2PD602ARL	2SC2001	2SD1628F-TD-H	2SK3069
2PD602ASL	2SC2120	2SD1628G-TD-E	2SK3070L
2SA1015	2SC2240	2SD1628G-TD-H	2SK3070S
2SA1020	2SC2655	2SD1805F-E	2SK30ATM
2SA1213	2SC2786	2SD1805F-TL-E	2SK3133
2SA1416S-TD-E	2SC2873	2SD1805G-E	2SK3134
2SA1416T-TD-E	2SC3649S-TD-E	2SD1805G-TL-E	2SK3135
2SA1460	2SC3649S-TD-H	2SD1815S-E	2SK3136
2SA1507S	2SC3649T-TD-E	2SD1815S-TL-E	2SK3140
2SA1507T	2SC3649T-TD-H	2SD1815T-E	2SK3141
2SA1774G	2SC3733	2SD1815T-TL-E	2SK3142
2SA1774T1G	2SC4617G	2SJ517	2SK3203
2SA2126-E	2SC4617T1G	2SJ652	2SK3233
2SA2126-H	2SC5566-TD-E	2SJ652-RA11	2SK330
2SA2126-TL-E	2SC5658M3T5G	2SJ661-E	2SK364
2SA2126-TL-H	2SC5706-E	2SJ665-DL-E	2SK366

Multisim 14.0 Full Components

2SK367	3 nF [C0805C302K3GACT U]	3.3 nF [C0603C332K1HACT U]	3.3 nF [C0805C332K2RACT U]
2SK368			
2SK3703	3 nF [C0805C302K3HACT U]	3.3 nF [C0603C332K1RACT U]	3.3 nF [C0805C332K3GACT U]
2SK3704			
2SK3746	3 nF [C0805C302K5HACT U]	3.3 nF [C0603C332K3GACT U]	3.3 nF [C0805C332K3HACT U]
2SK3746-1E			
2SK3747	3 nF [C1825C302KBGAC TU]	3.3 nF [C0603C332K3HACT U]	3.3 nF [C0805C332K4GACT U]
2SK3747-1E			
2SK3748	3 nF [C2220C302KBGAC TU]	3.3 nF [C0603C332K3RACT U]	3.3 nF [C0805C332K4RACT U]
2SK3748-1E			
2SK3820-DL-E	3 nF [C2225C302KBGAC TU]	3.3 nF [C0603C332K4RACT U]	3.3 nF [C0805C332K5GACT U]
2SK3820-E			
2V7002LT1G	3.3 nF [C0402C332K3RACT U]	3.3 nF [C0603C332K5HACT U]	3.3 nF [C0805C332K5HACT U]
2V7002LT3G			
3 nF [C0603C302K1HACT U]	3.3 nF [C0402C332K4RACT U]	3.3 nF [C0603C332K5RACT U]	3.3 nF [C0805C332K5RACT U]
3 nF [C0603C302K3HACT U]	3.3 nF [C0402C332K5RACT U]	3.3 nF [C0805C332K1GACT U]	3.3 nF [C0805C332K8GACT U]
3 nF [C0603C302K5HACT U]	3.3 nF [C0402C332K8RACT U]	3.3 nF [C0805C332K1HACT U]	3.3 nF [C0805C332KARACT U]
3 nF [C0805C302K1GACT U]	3.3 nF [C0402C332K9RACT U]	3.3 nF [C0805C332K1RACT U]	3.3 nF [C1206C332K1GACT U]
3 nF [C0805C302K1HACT U]			

Multisim 14.0 Full Components

3.3 nF [C1206C332K1RACT U]	3.3 nF [C2225C332KBGAC TU]	3.3 uF [C1206C335K9PACT U]	3.3 uF [T491A335M010AT]
3.3 nF [C1206C332K2RACT U]	3.3 nF [CA064C332K1RACT U]	3.3 uF [C1206C335K9RACT U]	3.3 uF [T491A335M016AT]
3.3 nF [C1206C332K3RACT U]	3.3 nF [CA064C332K5RACT U]	3.3 uF [C1206C335M4VAC TU]	3.3 uF [T491A335M020AT]
3.3 nF [C1206C332K5GACT U]	3.3 uF [C0805C335K4PACT U]	3.3 uF [C1206C335M9VAC TU]	3.3 uF [T491B335M016AT]
3.3 nF [C1206C332K5RACT U]	3.3 uF [C0805C335K8PACT U]	3.3 uF [C1210C335K3PACT U]	3.3 uF [T491B335M020AT]
3.3 nF [C1210C332K1RACT U]	3.3 uF [C0805C335K9PACT U]	3.3 uF [C1210C335K4PACT U]	3.3 uF [T491B335M025AT]
3.3 nF [C1210C332K2GACT U]	3.3 uF [C1206C335K3PACT U]	3.3 uF [C1210C335K4RACT U]	3.3 uF [T491B335M035AT]
3.3 nF [C1210C332K5GACT U]	3.3 uF [C1206C335K4PACT U]	3.3 uF [C1210C335K8PACT U]	3.3 uF [T491C335M016AT]
3.3 nF [C1210C332K5RACT U]	3.3 uF [C1206C335K4RACT U]	3.3 uF [T409B335M006AH 4250]	3.3 uF [T491C335M025AT]
3.3 nF [C1825C332KBGAC TU]	3.3 uF [C1206C335K8PACT U]	3.3 uF [T489A335M020AT E3K7]	3.3 uF [T491C335M035AT]
3.3 nF [C2220C332KBGAC TU]	3.3 uF [C1206C335K8RACT U]	3.3 uF [T491A335M004AT]	3.3 uF [T491D335M035AT]
		3.3 uF [T491A335M006AT]	3.3 uF [T491D335M050AT]
			3.3 uF [T491S335M010AT]
			3.3 uF [T491T335M020AT]
			3.3 uF [T493A335M004AH 6110]

Multisim 14.0 Full Components

3.3 uF [T494A335M004AT]	3.3 uF [T495B335M035AT E900]	3.6 nF [C0805C362K1HACT U]	3.9 nF [C0603C392K3GACT U]
3.3 uF [T494A335M006AT]	3.3 uF [T495C335M035AT E525]	3.6 nF [C0805C362K3HACT U]	3.9 nF [C0603C392K3HACT U]
3.3 uF [T494A335M010AT]	3.3 uF [T495C335M035AT E550]	3.6 nF [C0805C362K5HACT U]	3.9 nF [C0603C392K3RACT U]
3.3 uF [T494A335M020AT]	3.3 uF [T495C335M035AT E600]	3.6 nF [C1825C362KBGAC TU]	3.9 nF [C0603C392K4RACT U]
3.3 uF [T494B335M016AT]	3.3 uF [T498A335M010AT E3K6]	3.6 nF [C2220C362KBGAC TU]	3.9 nF [C0603C392K5HACT U]
3.3 uF [T494B335M025AT]	3.3 uF [T498A335M016AT E3K4]	3.6 nF [C2225C362KBGAC TU]	3.9 nF [C0603C392K5RACT U]
3.3 uF [T494B335M035AT]	3.3 uF [T498C335M035AT E1K7]	3.9 nF [C0402C392K3RACT U]	3.9 nF [C0805C392K1GACT U]
3.3 uF [T494C335M025AT]	3.6 nF [C0603C362K1HACT U]	3.9 nF [C0402C392K4RACT U]	3.9 nF [C0805C392K1HACT U]
3.3 uF [T494D335M050AT]	3.6 nF [C0603C362K3HACT U]	3.9 nF [C0402C392K5RACT U]	3.9 nF [C0805C392K1RACT U]
3.3 uF [T494S335M010AT]	3.6 nF [C0603C362K5HACT U]	3.9 nF [C0603C392K1HACT U]	3.9 nF [C0805C392K2RACT U]
3.3 uF [T494T335M020AT]	3.6 nF [C0805C362K1GACT U]	3.9 nF [C0603C392K1RACT U]	3.9 nF [C0805C392K3GACT U]
3.3 uF [T495A335M016AT E3K0]			

Multisim 14.0 Full Components

3.9 nF [C0805C392K3HACT U]	3.9 nF [C1206C392K5GACT U]	3.9 uF [C1206C395K9RACT U]	30 pF [C1206C300K5GACT U]
3.9 nF [C0805C392K3RACT U]	3.9 nF [C1206C392K5RACT U]	3.9 uF [C1210C395K3NAC TU]	30 pF [C1206C300KBGAC TU]
3.9 nF [C0805C392K4GACT U]	3.9 nF [C1210C392K5RACT U]	3_AMP 30 mF [C0402C309K5GACT U]	30 pF [C1210C300KBGAC TU]
3.9 nF [C0805C392K4RACT U]	3.9 nF [C1812C392K2GACT U]	30 mF [C0805C309KBGAC TU]	30 pF [C1812C300KBGAC TU]
3.9 nF [C0805C392K5GACT U]	3.9 nF [C1825C392KBGAC TU]	30 pF [C0402C300K5GACT U]	30 pF [C1825C300KBGAC TU]
3.9 nF [C0805C392K5HACT U]	3.9 nF [C2220C392KBGAC TU]	30 pF [C0603C300K2GACT U]	30 pF [C2220C300KBGAC TU]
3.9 nF [C0805C392K5RACT U]	3.9 nF [C2225C392KBGAC TU]	30 pF [C0603C300K5GACT U]	30 pF [C2225C300KBGAC TU]
3.9 nF [C0805C392KARACT U]	3.9 nF [C2225C392KCGAC TU]	30 pF [C0805C300K2GACT U]	30_AMP 300 pF [C0402C301K1HACT U]
3.9 nF [C1206C392K1GACT U]	3.9 nF [CDR02BX392BKSM]	30 pF [C0805C300K5GACT U]	300 pF [C0402C301K3HACT U]
3.9 nF [C1206C392K1RACT U]	3.9 uF [C1206C395K4RACT U]	30 pF [C0805C300KBGAC TU]	300 pF [C0402C301K5HACT U]
3.9 nF [C1206C392K2RACT U]	3.9 uF [C1206C395K8RACT U]	30 pF [C1206C300K1GACT U]	300 pF [C0805C301K1GACT U]

Multisim 14.0 Full Components

300 pF [C0805C301K2GACT U]	33 mF [C1206C339K5GACT U]	33 nF [C0603C333K8RACT U]	33 nF [C0805F333K1RACT U]
300 pF [C0805C301K5GACT U]	33 nF [C0402C333K3RACT U]	33 nF [C0603C333M3VAC TU]	33 nF [C0805F333K3RACT U]
300 pF [C1206C301K5GACT U]	33 nF [C0402C333K4RACT U]	33 nF [C0805C333K1RACT U]	33 nF [C0805F333K4RACT U]
300 pF [C1206C301KBGAC TU]	33 nF [C0402C333K8PACT U]	33 nF [C0805C333K2RACT U]	33 nF [C0805F333K5RACT U]
300 pF [C1210C301KBGAC TU]	33 nF [C0402C333K8RACT U]	33 nF [C0805C333K3GACT U]	33 nF [C1206C333K1HACT U]
300 pF [C1812C301KBGAC TU]	33 nF [C0402C333K9PACT U]	33 nF [C0805C333K3HACT U]	33 nF [C1206C333K1RACT U]
300 pF [C1825C301KBGAC TU]	33 nF [C0402C333K9RACT U]	33 nF [C0805C333K3RACT U]	33 nF [C1206C333K2RACT U]
300 pF [C2220C301KBGAC TU]	33 nF [C0603C333K1RACT U]	33 nF [C0805C333K4RACT U]	33 nF [C1206C333K3GACT U]
300 pF [C2225C301KBGAC TU]	33 nF [C0603C333K3RACT U]	33 nF [C0805C333K5RACT U]	33 nF [C1206C333K3HACT U]
30V_10W	33 nF [C0603C333K4RACT U]	33 nF [C0805C333K8RACT U]	33 nF [C1206C333K5HACT U]
3280A			
3288RT	33 nF [C0603C333K5RACT U]	33 nF [C0805C333M5UAC TU]	33 nF [C1206C333K5RACT U]
33 mF [C0805C339KBGAC TU]			

Multisim 14.0 Full Components

33 nF [C1206C333KARACT U]	33 nF [C1210C333K5RACT U]	33 nF [C2220C333K1GACT U]	33 pF [C0603C330K2GACT U]
33 nF [C1206C333M1UAC TU]	33 nF [C1210C333KARACT U]	33 nF [C2220C333K2GACT U]	33 pF [C0603C330K3GACT U]
33 nF [C1206C333M5UAC TU]	33 nF [C1812C333K1GACT U]	33 nF [C2220C333K5GACT U]	33 pF [C0603C330K5GACT U]
33 nF [C1210C333K1GACT U]	33 nF [C1812C333K1HACT U]	33 nF [C2225C333K5GACT U]	33 pF [C0805C330K1GACT U]
33 nF [C1210C333K1HACT U]	33 nF [C1812C333K1RACT U]	33 nF [CA064C333K4RACT U]	33 pF [C0805C330K2GACT U]
33 nF [C1210C333K1RACT U]	33 nF [C1812C333K2RACT U]	33 pF [C0201C330K3GACT U]	33 pF [C0805C330K5GACT U]
33 nF [C1210C333K2RACT U]	33 nF [C1812C333K5GACT U]	33 pF [C0402C330K3GACT U]	33 pF [C0805C330KBGAC TU]
33 nF [C1210C333K3GACT U]	33 nF [C1812C333K5HACT U]	33 pF [C0402C330K4GACT U]	33 pF [C0805C330KDGAC TU]
33 nF [C1210C333K3HACT U]	33 nF [C1812C333K5RACT U]	33 pF [C0402C330K5GACT U]	33 pF [C1206C330K1GACT U]
33 nF [C1210C333K5GACT U]	33 nF [C1825C333K1RACT U]	33 pF [C0402C330K8GACT U]	33 pF [C1206C330K2GACT U]
33 nF [C1210C333K5HACT U]	33 nF [C1825C333K5RACT U]	33 pF [C0603C330K1GACT U]	33 pF [C1206C330K5GACT U]

Multisim 14.0 Full Components

33 pF [C1206C330KBGAC TU]	33 uF [A700V336M006AT E018]	33 uF [T419E336M006AH 4250]	33 uF [T491C336M016AT]
33 pF [C1206C330KCGAC TU]	33 uF [A700V336M006AT E025]	33 uF [T419X336M025AH 4250]	33 uF [T491C336M020AT]
33 pF [C1206C330KDGAC TU]	33 uF [A700V336M006AT E028]	33 uF [T489D336M020AT E250]	33 uF [T491D336M010AT]
33 pF [C1206C330KGGAC TU]	33 uF [A700V336M008AT E018]	33 uF [T491A336M003AT]	33 uF [T491D336M016AT]
33 pF [C1210C330KBGAC TU]	33 uF [A700V336M008AT E025]	33 uF [T491A336M004AT]	33 uF [T491D336M020AT]
33 pF [C1812C330KBGAC TU]	33 uF [A700V336M008AT E028]	33 uF [T491A336M010AT]	33 uF [T491D336M025AT]
33 pF [C1825C330KBGAC TU]	33 uF [A700V336M010AT E018]	33 uF [T491B336M004AT]	33 uF [T491D336M035AT]
33 pF [C2220C330KBGAC TU]	33 uF [A700V336M010AT E025]	33 uF [T491B336M006AT]	33 uF [T491T336M004AT]
33 pF [C2225C330KBGAC TU]	33 uF [A700V336M010AT E028]	33 uF [T491B336M016AT]	33 uF [T491T336M006AT]
33 pF [CA064C330K5GAC TU]	33 uF [T409F336M004AH 4250]	33 uF [T491C336M004AT]	33 uF [T491T336M010AT]
33 pF [CA064C330K8GAC TU]	33 uF [T409G336M010AH 4250]	33 uF [T491C336M006AT]	33 uF [T491U336M004AT]
		33 uF [T491C336M010AT]	33 uF [T491U336M006AT]

Multisim 14.0 Full Components

33 uF [T491U336M010AT]	33 uF [T494C336M010AT]	33 uF [T494U336M006AT]	33 uF [T495D336M020AT E200]
33 uF [T491U336M016AT]	33 uF [T494C336M016AT]	33 uF [T494U336M010AT]	33 uF [T495D336M025AT E090]
33 uF [T491V336M010AT]	33 uF [T494C336M025AT]	33 uF [T494U336M016AT]	33 uF [T495D336M025AT E100]
33 uF [T491V336M020AT]	33 uF [T494D336M010AT]	33 uF [T494V336M010AT]	33 uF [T495D336M025AT E225]
33 uF [T491X336M025AT]	33 uF [T494D336M016AT]	33 uF [T494V336M020AT]	33 uF [T495D336M025AT E300]
33 uF [T491X336M035AT]	33 uF [T494D336M020AT]	33 uF [T494X336M025AT]	33 uF [T495E336M035AT E200]
33 uF [T494A336M003AT]	33 uF [T494D336M025AT]	33 uF [T495B336M010AT E450]	33 uF [T495V336M010AT E100]
33 uF [T494A336M004AT]	33 uF [T494D336M035AT]	33 uF [T495C336M016AT E200]	33 uF [T495V336M010AT E150]
33 uF [T494A336M006AT]	33 uF [T494T336M004AT]	33 uF [T495C336M016AT E275]	33 uF [T495X336M025AT E100]
33 uF [T494B336M004AT]	33 uF [T494T336M006AT]	33 uF [T495D336M016AT E225]	33 uF [T495X336M025AT E175]
33 uF [T494B336M006AT]	33 uF [T494T336M010AT]	33 uF [T495D336M020AT E100]	33 uF [T495X336M025AT E200]
33 uF [T494B336M010AT]	33 uF [T494U336M004AT]		
33 uF [T494C336M004AT]			
33 uF [T494C336M006AT]			

Multisim 14.0 Full Components

33 uF [T495X336M035AT E100]	33 uF [T520A336M004AT E080]	33 uF [T520B336M010AT E035]	33 uF [T520V336M016AT E045]
33 uF [T495X336M035AT E175]	33 uF [T520A336M006AT E070]	33 uF [T520B336M010AT E040]	33 uF [T520V336M016AT E060]
33 uF [T495X336M035AT E250]	33 uF [T520A336M006AT E080]	33 uF [T520B336M010AT E070]	33 uF [T520V336M016AT E070]
33 uF [T497H336M015AT 6110]	33 uF [T520B336M006AT E025]	33 uF [T520C336M006AT E100]	33 uF [T520W336M016AT E045]
33 uF [T498B336M006AT E1K7]	33 uF [T520B336M006AT E035]	33 uF [T520T336M006AT E070]	33 uF [T521D336M025AT E060]
33 uF [T498D336M016AT E600]	33 uF [T520B336M006AT E040]	33 uF [T520T336M008AT E070]	33 uF [T521D336M035AT E065]
33 uF [T498D336M025AT E600]	33 uF [T520B336M006AT E070]	33 uF [T520T336M008AT E080]	33 uF [T521V336M025AT E060]
33 uF [T498X336M035AT E500]	33 uF [T520B336M008AT E025]	33 uF [T520T336M010AT E070]	33 uF [T525B336M006AT E080]
33 uF [T510X336M035AT E050]	33 uF [T520B336M008AT E035]	33 uF [T520T336M010AT E080]	33 uF [T525B336M010AT E080]
33 uF [T510X336M035AT E065]	33 uF [T520B336M008AT E040]	33 uF [T520U336M008AT E070]	33 uF [T525T336M008AT E080]
33 uF [T520A336M004AT E070]	33 uF [T520B336M008AT E070]	33 uF [T520U336M010AT E070]	33 uF [T525T336M010AT E080]

Multisim 14.0 Full Components

33 uF [T528I336M010ATE 150]	330 nF [C0805C334K4RACT U]	330 nF [C1206F334K4RACT U]	330 nF [C1812C334K5RACT U]
33 uF [T541X336M050AH 6510]	330 nF [C0805C334K8RACT U]	330 nF [C1210C334K1RACT U]	330 nF [C1812C334KARACT U]
33 uF [T543A336M004AT E070]	330 nF [C0805C334M3VAC TU]	330 nF [C1210C334K3RACT U]	330 nF [C1812C334M5UAC TU]
33 uF [T543B336M010AT E040]	330 nF [C0805C334M4VAC TU]	330 nF [C1210C334K5RACT U]	330 nF [C1812F334K1RACT U]
330 nF [C0603C334K4PACT U]	330 nF [C0805C334M8VAC TU]	330 nF [C1210C334M5UAC TU]	330 nF [C1812F334K2RACT U]
330 nF [C0603C334K4RACT U]	330 nF [C1206C334K1RACT U]	330 nF [C1210C334M5VAC TU]	330 nF [C1812F334K3RACT U]
330 nF [C0603C334K8PACT U]	330 nF [C1206C334K3RACT U]	330 nF [C1210F334K1RACT U]	330 nF [C1812F334K5RACT U]
330 nF [C0603C334K8RACT U]	330 nF [C1206C334K4RACT U]	330 nF [C1210F334K3RACT U]	330 nF [C1825C334K1RACT U]
330 nF [C0603C334K9RACT U]	330 nF [C1206C334K5RACT U]	330 nF [C1210F334K4RACT U]	330 nF [C1825C334K2RACT U]
330 nF [C0805C334K3NAC TU]	330 nF [C1206C334M3VAC TU]	330 nF [C1210F334K5RACT U]	330 nF [C1825C334K5RACT U]
330 nF [C0805C334K3RACT U]	330 nF [C1206F334K3RACT U]	330 nF [C1812C334K1RACT U]	330 nF [C1825C334M5UAC TU]

Multisim 14.0 Full Components

330 nF [C2220C334K1GACT U]	330 nF [T491B334M050AT]	330 pF [C0402C331K5RACT U]	330 pF [C0805C331K1RACT U]
330 nF [C2220C334K1RACT U]	330 nF [T494A334M025AT]	330 pF [C0402C331K8RACT U]	330 pF [C0805C331K2GACT U]
330 nF [C2220C334K2RACT U]	330 nF [T494B334M050AT]	330 pF [C0603C331K1RACT U]	330 pF [C0805C331K2RACT U]
330 nF [C2220C334K5GACT U]	330 nF [T496B334M050AT 6110]	330 pF [C0603C331K2RACT U]	330 pF [C0805C331K3GACT U]
330 nF [C2220C334K5RACT U]	330 pF [C0402C331K1HACT U]	330 pF [C0603C331K3GACT U]	330 pF [C0805C331K3RACT U]
330 nF [C2225C334K1RACT U]	330 pF [C0402C331K3HACT U]	330 pF [C0603C331K3RACT U]	330 pF [C0805C331K4RACT U]
330 nF [C2225C334K2RACT U]	330 pF [C0402C331K3RACT U]	330 pF [C0603C331K4RACT U]	330 pF [C0805C331K5GACT U]
330 nF [C2225C334K5RACT U]	330 pF [C0402C331K4GACT U]	330 pF [C0603C331K5GACT U]	330 pF [C0805C331K5RACT U]
330 nF [C2225C334M5UAC TU]	330 pF [C0402C331K4RACT U]	330 pF [C0603C331K5RACT U]	330 pF [C0805C331K8RACT U]
330 nF [T409A334M025AH 4250]	330 pF [C0402C331K5GACT U]	330 pF [C0603C331K8RACT U]	330 pF [C1206C331K1GACT U]
330 nF [T491A334M025AT]	330 pF [C0402C331K5HACT U]	330 pF [C0805C331K1GACT U]	330 pF [C1206C331K2GACT U]
330 nF [T491A334M035AT]			

Multisim 14.0 Full Components

330 pF [C1206C331K5GACT U]	330 pF [CA064C331K5RACT U]	330 uF [T491D337M006AT]	330 uF [T494V337M004AT]
330 pF [C1206C331KBGAC TU]	330 uF [A700D337M002AT E007]	330 uF [T491D337M010AT]	330 uF [T494X337M006AT]
330 pF [C1206C331KCGAC TU]	330 uF [A700X337M002AT E010]	330 uF [T491E337M006AT]	330 uF [T495D337M004AT E030]
330 pF [C1210C331K1GACT U]	330 uF [A700X337M002AT E015]	330 uF [T491E337M010AT]	330 uF [T495D337M006AT E040]
330 pF [C1210C331K5GACT U]	330 uF [A700X337M004AT E010]	330 uF [T491X337M006AT]	330 uF [T495D337M006AT E050]
330 pF [C1210C331KBGAC TU]	330 uF [A700X337M004AT E015]	330 uF [T491X337M010AT]	330 uF [T495D337M006AT E070]
330 pF [C1812C331KBGAC TU]	330 uF [A700X337M2R5AT E010]	330 uF [T494D337M004AT]	330 uF [T495D337M006AT E100]
330 pF [C1825C331KBGAC TU]	330 uF [A700X337M2R5AT E015]	330 uF [T494D337M006AT]	330 uF [T495D337M010AT E100]
330 pF [C2220C331KBGAC TU]	330 uF [T489X337M010AT E100]	330 uF [T494D337M010AT]	330 uF [T495D337M010AT E125]
330 pF [C2225C331KBGAC TU]	330 uF [T491C337M004AT]	330 uF [T494E337M006AT]	330 uF [T495D337M010AT E150]
330 pF [CA064C331K5GACT TU]	330 uF [T491D337M004AT]	330 uF [T494E337M010AT]	330 uF [T495E337M010AT E060]

Multisim 14.0 Full Components

330 uF [T495X337M006AT E045]	330 uF [T520C337M004AT E025]	330 uF [T520D337M006AT E009]	330 uF [T520V337M003AT E009]
330 uF [T495X337M006AT E065]	330 uF [T520C337M2R5AT E015]	330 uF [T520D337M006AT E010]	330 uF [T520V337M003AT E012]
330 uF [T495X337M006AT E100]	330 uF [T520C337M2R5AT E025]	330 uF [T520D337M006AT E015]	330 uF [T520V337M003AT E015]
330 uF [T495X337M010AT E035]	330 uF [T520C337M2R5AT E045]	330 uF [T520D337M006AT E025]	330 uF [T520V337M003AT E025]
330 uF [T495X337M010AT E050]	330 uF [T520D337M004AT E006]	330 uF [T520D337M006AT E040]	330 uF [T520V337M004AT E007]
330 uF [T495X337M010AT E060]	330 uF [T520D337M004AT E007]	330 uF [T520D337M006AT E045]	330 uF [T520V337M004AT E009]
330 uF [T495X337M010AT E100]	330 uF [T520D337M004AT E009]	330 uF [T520D337M2R5AT E006]	330 uF [T520V337M004AT E012]
330 uF [T510X337M010AT E035]	330 uF [T520D337M004AT E012]	330 uF [T520D337M2R5AT E007]	330 uF [T520V337M004AT E018]
330 uF [T513X337M010AH 6110]	330 uF [T520D337M004AT E015]	330 uF [T520L337M2R5AT E009]	330 uF [T520V337M004AT E025]
330 uF [T520B337M2R5AT E045]	330 uF [T520D337M004AT E040]	330 uF [T520L337M2R5AT E012]	330 uF [T520V337M004AT E040]
330 uF [T520B337M2R5AT E070]	330 uF [T520D337M004AT E045]	330 uF [T520L337M2R5AT E025]	330 uF [T520V337M006AT E015]

Multisim 14.0 Full Components

330 uF [T520V337M006AT E025]	330 uF [T520W337M2R5A TE040]	330 uF [T525D337M004AT E025]	330 uF [T530D337M004AT E006]
330 uF [T520V337M006AT E040]	330 uF [T520X337M010AT E010]	330 uF [T525D337M006AT E025]	330 uF [T530D337M006AT E006]
330 uF [T520V337M2R5AT E006]	330 uF [T520X337M010AT E025]	330 uF [T525D337M006AT E040]	330 uF [T530D337M006AT E010]
330 uF [T520V337M2R5AT E007]	330 uF [T520X337M010AT E040]	330 uF [T525D337M2R5AT E025]	330 uF [T530X337M010AT E004]
330 uF [T520V337M2R5AT E009]	330 uF [T520Y337M006AT E015]	330 uF [T528Z337M004AT E009]	330 uF [T530X337M010AT E005]
330 uF [T520V337M2R5AT E012]	330 uF [T520Y337M006AT E025]	330 uF [T528Z337M004AT E012]	330 uF [T530X337M010AT E006]
330 uF [T520V337M2R5AT E015]	330 uF [T520Y337M006AT E040]	330 uF [T528Z337M2R5AT E005]	330 uF [T530X337M010AT E010]
330 uF [T520V337M2R5AT E018]	330 uF [T520Y337M010AT E015]	330 uF [T528Z337M2R5AT E007]	330 uF [T530Y337M006AT E006]
330 uF [T520V337M2R5AT E025]	330 uF [T520Y337M010AT E035]	330 uF [T528Z337M2R5AT E008]	330 uF [T541X337M010AH 6520]
330 uF [T520V337M2R5AT E040]	330 uF [T522V337M006AT E040]	330 uF [T528Z337M2R5AT E009]	330 uF [T541Y337M006AH 6510]
330 uF [T520W337M2R5A TE025]	330 uF [T525D337M003AT E025]	330 uF [T528Z337M2R5AT E012]	330 uF [T543C337M2R5AT E045]

Multisim 14.0 Full Components

330 uF [T543L337M2R5AT E025]	36 pF [C2220C360KZGACT U]	360 pF [C2225C361KBGAC TU]	39 nF [C0805C393K1RACT U]
330 uF [T543Y337M006AT E015]	36 pF [C2225C360KBGAC TU]	3-644456-5 3-644456-8	39 nF [C0805C393K3RACT U]
3-534206-0 3554AM	360 pF [C0402C361K1HACT U]	39 mF [C0805C399KBGAC TU]	39 nF [C0805C393K4RACT U]
3554BM 3554SM	360 pF [C0402C361K3HACT U]	39 nF [C0402C393K4RACT U]	39 nF [C0805C393K5RACT U]
36 mF [C0805C369KBGAC TU]	360 pF [C0402C361K5HACT U]	39 nF [C0402C393K8RACT U]	39 nF [C0805C393K8RACT U]
36 pF [C0805C360KBGAC TU]	360 pF [C0603C361K5GACT U]	39 nF [C0402C393K9RACT U]	39 nF [C0805F393K1RACT U]
36 pF [C1206C360KBGAC TU]	360 pF [C1206C361KBGAC TU]	39 nF [C0603C393K1RACT U]	39 nF [C0805F393K3RACT U]
36 pF [C1210C360KBGAC TU]	360 pF [C1210C361KBGAC TU]	39 nF [C0603C393K3RACT U]	39 nF [C0805F393K4RACT U]
36 pF [C1812C360KBGAC TU]	360 pF [C1812C361KBGAC TU]	39 nF [C0603C393K4RACT U]	39 nF [C0805F393K5RACT U]
36 pF [C1825C360KBGAC TU]	360 pF [C1825C361KBGAC TU]	39 nF [C0603C393K5RACT U]	39 nF [C1206C393K1RACT U]
36 pF [C2220C360KBGAC TU]	360 pF [C2220C361KBGAC TU]	39 nF [C0603C393K8RACT U]	39 nF [C1206C393K4RACT U]

Multisim 14.0 Full Components

39 nF [C1206C393K5RACT U]	39 pF [C0402C390K4GACT U]	39 pF [C1206C390K2GACT U]	390 nF [C0603C394K8PACT U]
39 nF [C1206C393KARACT U]	39 pF [C0402C390K5GACT U]	39 pF [C1206C390K5GACT U]	390 nF [C0603C394K8RACT U]
39 nF [C1206C393M1UAC TU]	39 pF [C0402C390K8GACT U]	39 pF [C1206C390KBGAC TU]	390 nF [C0603C394K9RACT U]
39 nF [C1210C393K1RACT U]	39 pF [C0603C390K2GACT U]	39 pF [C1210C390KBGAC TU]	390 nF [C0805C394K3RACT U]
39 nF [C1210C393K2RACT U]	39 pF [C0603C390K5GACT U]	39 pF [C1812C390KBGAC TU]	390 nF [C0805C394K4RACT U]
39 nF [C1210C393K5RACT U]	39 pF [C0805C390K1GACT U]	39 pF [C1825C390KBGAC TU]	390 nF [C0805C394K8RACT U]
39 nF [C1210C393KARACT U]	39 pF [C0805C390K2GACT U]	39 pF [C2220C390KBGAC TU]	390 nF [C0805C394K9RACT U]
39 nF [C1812C393K1RACT U]	39 pF [C0805C390K5GACT U]	39 pF [C2225C390KBGAC TU]	390 nF [C1206C394K1RACT U]
39 nF [C1812C393K5RACT U]	39 pF [C0805C390KBGAC TU]	39 pF [CA064C390K5GAC TU]	390 nF [C1206C394K3RACT U]
39 nF [C2220C393K2GACT U]	39 pF [C0805C390KCGAC TU]	390 nF [C0603C394K4PACT U]	390 nF [C1206C394K4RACT U]
39 pF [C0201C390K3GACT U]	39 pF [C1206C390K1GACT U]	390 nF [C0603C394K4RACT U]	390 nF [C1206C394K5RACT U]

Multisim 14.0 Full Components

390 nF [C1206C394K8RACT U]	390 nF [C1812C394M5UAC TU]	390 pF [C0402C391K3HACT U]	390 pF [C0603C391K5RACT U]
390 nF [C1206F394K3RACT U]	390 nF [C1812F394K1RACT U]	390 pF [C0402C391K3RACT U]	390 pF [C0805C391K1GACT U]
390 nF [C1206F394K4RACT U]	390 nF [C1812F394K2RACT U]	390 pF [C0402C391K4RACT U]	390 pF [C0805C391K1RACT U]
390 nF [C1210C394K3RACT U]	390 nF [C1812F394K3RACT U]	390 pF [C0402C391K5HACT U]	390 pF [C0805C391K2GACT U]
390 nF [C1210C394K5RACT U]	390 nF [C1812F394K5RACT U]	390 pF [C0402C391K5RACT U]	390 pF [C0805C391K4RACT U]
390 nF [C1210F394K3RACT U]	390 nF [C1825C394K1RACT U]	390 pF [C0603C391K1RACT U]	390 pF [C0805C391K5GACT U]
390 nF [C1210F394K4RACT U]	390 nF [C1825C394K2RACT U]	390 pF [C0603C391K2RACT U]	390 pF [C0805C391K5RACT U]
390 nF [C1210F394K5RACT U]	390 nF [C1825C394K5RACT U]	390 pF [C0603C391K3GACT U]	390 pF [C1206C391K1GACT U]
390 nF [C1812C394K1RACT U]	390 nF [C2225C394K1RACT U]	390 pF [C0603C391K3RACT U]	390 pF [C1206C391K2GACT U]
390 nF [C1812C394K5RACT U]	390 nF [C2225C394K2RACT U]	390 pF [C0603C391K4RACT U]	390 pF [C1206C391K5GACT U]
390 nF [C1812C394KARACT U]	390 pF [C0402C391K1HACT U]	390 pF [C0603C391K5GACT U]	390 pF [C1206C391KBGAC TU]

Multisim 14.0 Full Components

390 pF [C1206C391KCGAC TU]	3KASMC24AHE3/9A T	3N259 3PDT_DB	4.3 nF [C2225C432KBGAC TU]
390 pF [C1210C391KBGAC TU]	3KASMC28AHM3/5 7T	3PDT_SB	4.7 nF [C0402C472K3RACT U]
390 pF [C1812C391KBGAC TU]	3Line_Bussed	3PST_DB	4.7 nF [C0402C472K4RACT U]
390 pF [C1825C391KBGAC TU]	3Line_Isolated	3PST_SB	4.7 nF [C0402C472K5RACT U]
390 pF [C1825C391KBGAC TU]	3LN01M-TL-E	4.3 nF [C0603C432K1HACT U]	4.7 nF [C0402C472K8RACT U]
390 pF [C2220C391KBGAC TU]	3LN01M-TL-H	4.3 nF [C0603C432K3HACT U]	4.7 nF [C0402C472K9RACT U]
390 pF [C2225C391KBGAC TU]	3LN01SS-TL-E	4.3 nF [C0603C432K5HACT U]	4.7 nF [C0603C472K1HACT U]
390 pF [C2225C391KBGAC TU]	3LN01SS-TL-H	4.3 nF [C0805C432K1GACT U]	4.7 nF [C0603C472K3HACT U]
390 pF [CA064C391K5GAC TU]	3LP01SS-TL-E	4.3 nF [C0805C432K3HACT U]	4.7 nF [C0603C472K1RACT U]
390 pF [A700X397M002AT E010]	3LP01SS-TL-H	4.3 nF [C0805C432K5HACT U]	4.7 nF [C0603C472K3GACT U]
390 pF [A700X397M002AT E015]	3LP01S-TL-E	4.3 nF [C1825C432KBGAC TU]	4.7 nF [C0603C472K3RACT U]
390 uF [A700X397M002AT E010]	3N246	4.3 nF [C2220C432KBGAC TU]	
390 uF [A700X397M002AT E015]	3N247		
3BH41	3N248		
3GH41	3N249		
3JH41	3N250		
3KASMC15AHE3/57 T	3N251		
	3N252		
	3N253		
	3N254		
	3N255		
	3N256		
	3N257		
	3N258		

Multisim 14.0 Full Components

4.7 nF [C0603C472K4RACT U]	4.7 nF [C0805C472K3RACT U]	4.7 nF [C1210C472K1GACT U]	4.7 nF [C2225C472K2GACT U]
4.7 nF [C0603C472K5HACT U]	4.7 nF [C0805C472K4RACT U]	4.7 nF [C1210C472K1RACT U]	4.7 nF [C2225C472KBGAC TU]
4.7 nF [C0603C472K5RACT U]	4.7 nF [C0805C472K5HACT U]	4.7 nF [C1210C472K2RACT U]	4.7 nF [CA064C472K3RACT U]
4.7 nF [C0603C472K8RACT U]	4.7 nF [C0805C472K5RACT U]	4.7 nF [C1210C472K5GACT U]	4.7 nF [CA064C472K5RACT U]
4.7 nF [C0603C472K9RACT U]	4.7 nF [C0805C472KARACT U]	4.7 nF [C1210C472K5RACT U]	4.7 uF [C0603C475K8PACT U]
4.7 nF [C0805C472K1GACT U]	4.7 nF [C1206C472K1RACT U]	4.7 nF [C1812C472K1GACT U]	4.7 uF [C0603C475K9PACT U]
4.7 nF [C0805C472K1HACT U]	4.7 nF [C1206C472K2RACT U]	4.7 nF [C1812C472K2GACT U]	4.7 uF [C0805C475K3PACT U]
4.7 nF [C0805C472K1RACT U]	4.7 nF [C1206C472K3RACT U]	4.7 nF [C1812C472K5GACT U]	4.7 uF [C0805C475K4PACT U]
4.7 nF [C0805C472K2RACT U]	4.7 nF [C1206C472K4GACT U]	4.7 nF [C1825C472K2GACT U]	4.7 uF [C0805C475K8PACT U]
4.7 nF [C0805C472K3GACT U]	4.7 nF [C1206C472K5GACT U]	4.7 nF [C1825C472KBGAC TU]	4.7 uF [C0805C475K9PACT U]
4.7 nF [C0805C472K3HACT U]	4.7 nF [C1206C472K5RACT U]	4.7 nF [C2220C472KBGAC TU]	4.7 uF [C1206C475K3PACT U]

Multisim 14.0 Full Components

4.7 uF [C1206C475K3RACT U]	4.7 uF [C1210C475K3RACT U]	4.7 uF [T409D475M010AH 4250]	4.7 uF [T491D475M035AT]
4.7 uF [C1206C475K4PACT U]	4.7 uF [C1210C475K4PACT U]	4.7 uF [T429C475M006AH 4250]	4.7 uF [T491D475M050AT]
4.7 uF [C1206C475K4RACT U]	4.7 uF [C1210C475K4RACT U]	4.7 uF [T491A475M004AT]	4.7 uF [T491S475M006AT]
4.7 uF [C1206C475K5PACT U]	4.7 uF [C1210C475K5R1C7 186]	4.7 uF [T491A475M006AT]	4.7 uF [T491S475M010AT]
4.7 uF [C1206C475K8NAC TU]	4.7 uF [C1210C475K5RACT U]	4.7 uF [T491A475M016AT]	4.7 uF [T491T475M016AT]
4.7 uF [C1206C475K8PACT U]	4.7 uF [C1210C475K8PACT U]	4.7 uF [T491A475M020AT]	4.7 uF [T494A475M006AT]
4.7 uF [C1206C475K8RACT U]	4.7 uF [C1210C475K8RACT U]	4.7 uF [T491A475M025AT]	4.7 uF [T494A475M010AT]
4.7 uF [C1206C475K9PACT U]	4.7 uF [C1210C475K9PACT U]	4.7 uF [T491B475M010AT]	4.7 uF [T494A475M016AT]
4.7 uF [C1206C475K9RACT U]	4.7 uF [C1210C475K9RACT U]	4.7 uF [T491B475M016AT]	4.7 uF [T494A475M020AT]
4.7 uF [C1210C475K3NAC TU]	4.7 uF [C1210C475M4VAC TU]	4.7 uF [T491B475M020AT]	4.7 uF [T494A475M025AT]
4.7 uF [C1210C475K3PACT U]	4.7 uF [C1210C475M8VAC TU]	4.7 uF [T491B475M025AT]	4.7 uF [T494B475M010AT]
		4.7 uF [T491C475M020AT]	4.7 uF [T494B475M016AT]
		4.7 uF [T491C475M025AT]	4.7 uF [T494B475M020AT]
		4.7 uF [T491C475M035AT]	4.7 uF [T494B475M025AT]

Multisim 14.0 Full Components

4.7 uF [T494C475M020AT]	4.7 uF [T495D475M050AT E275]	4000BP_10V	4002BT_15V
4.7 uF [T494C475M025AT]	4.7 uF [T495D475M050AT E300]	4000BP_15V	4002BT_5V
4.7 uF [T494C475M035AT]	4.7 uF [T495X475M050AT E300]	4000BP_5V	4008BD_10V
4.7 uF [T494D475M035AT]	4.7 uF [T498A475M010AT E2K9]	4000BP_5V	4008BD_15V
4.7 uF [T494D475M050AT]	4.7 uF [T498B475M010AT E2K7]	4000BT_10V	4008BD_5V
4.7 uF [T494S475M006AT]	4.7 uF [T498B475M016AT E2K1]	4000BT_15V	4008BP_10V
4.7 uF [T494S475M010AT]	4.7 uF [T521D475M063AT E075]	4000BT_5V	4008BP_15V
4.7 uF [T494T475M016AT]	4.7 uF [T521D475M063AT E300]	4001BD_10V	4008BP_5V
4.7 uF [T495A475M010AT E1K3]	4.7 uF [T540D475M063AH 6510]	4001BD_15V	4008BP_5V
4.7 uF [T495B475M016AT E700]	4 AMP	4001BD_5V	4008BT_10V
4.7 uF [T495C475M035AT E450]	40 AMP	4001BP_10V	4008BT_15V
4.7 uF [T495C475M035AT E500]	4000BD_10V	4001BP_15V	4008BT_5V
4.7 uF [T495C475M035AT E600]	4000BD_15V	4001BP_5V	4009BCL_10V
	4000BD_5V	4001BT_10V	4009BCL_15V
		4001BT_15V	4009BCL_5V
		4001BT_5V	4009BCP_10V
		4002BD_10V	4009BCP_15V
		4002BD_15V	4009BCP_5V
		4002BD_5V	4009BD_10V
		4002BP_10V	4009BD_15V
		4002BP_15V	4009BD_5V
		4002BP_5V	40106BD_10V
		4002BT_10V	40106BD_15V
			40106BD_5V

Multisim 14.0 Full Components

40106BP_10V	4011BP_5V	4014BD_10V	4017BP_15V
40106BP_15V	4011BP_5V	4014BD_15V	4017BP_5V
40106BP_5V	4011BT_10V	4014BD_5V	4017BP_5V
40106BP_5V	4011BT_15V	4014BP_10V	4017BT_10V
40106BT_10V	4011BT_5V	4014BP_15V	4017BT_15V
40106BT_15V	4012BD_10V	4014BP_5V	4017BT_5V
40106BT_5V	4012BD_15V	4014BP_5V	4019BD_10V
4010BC1_10V	4012BD_5V	4014BT_10V	4019BD_15V
4010BC1_15V	4012BP_10V	4014BT_15V	4019BD_5V
4010BC1_5V	4012BP_15V	4014BT_5V	4019BP_10V
4010BEY_10V	4012BP_5V	4015BD_10V	4019BP_15V
4010BEY_15V	4012BP_5V	4015BD_15V	4019BP_5V
4010BEY_5V	4012BT_10V	4015BD_5V	4019BP_5V
4010BF_10V	4012BT_15V	4015BP_10V	4019BT_10V
4010BF_15V	4012BT_5V	4015BP_15V	4019BT_15V
4010BF_5V	4013BD_10V	4015BP_5V	4019BT_5V
4010BF_5V	4013BD_15V	4015BP_5V	4023BD_10V
4010BM1_10V	4013BD_5V	4015BT_10V	4023BD_15V
4010BM1_15V	4013BP_10V	4015BT_15V	4023BD_5V
4010BM1_5V	4013BP_15V	4015BT_5V	4023BP_10V
4011BD_10V	4013BP_5V	4017BD_10V	4023BP_15V
4011BD_15V	4013BP_5V	4017BD_15V	4023BP_5V
4011BD_5V	4013BT_10V	4017BD_5V	4023BP_5V
4011BP_10V	4013BT_15V	4017BP_10V	4023BT_10V
4011BP_15V	4013BT_5V	4017BP_10V	4023BT_15V

Multisim 14.0 Full Components

4023BT_5V	4027BP_15V	4030BT_5V	4042BP_15V
4024BD_10V	4027BP_5V	4040BD_10V	4042BP_5V
4024BD_15V	4027BP_5V	4040BD_15V	4042BP_5V
4024BD_5V	4027BT_10V	4040BD_5V	4042BT_10V
4024BP_10V	4027BT_15V	4040BP_10V	4042BT_15V
4024BP_15V	4027BT_5V	4040BP_15V	4042BT_5V
4024BP_5V	4028BD_10V	4040BP_5V	4043BD_10V
4024BP_5V	4028BD_15V	4040BP_5V	4043BD_15V
4024BT_10V	4028BD_5V	4040BT_10V	4043BD_5V
4024BT_15V	4028BP_10V	4040BT_15V	4043BP_10V
4024BT_5V	4028BP_15V	4040BT_5V	4043BP_15V
4025BD_10V	4028BP_5V	4041BD_10V	4043BP_5V
4025BD_15V	4028BP_5V	4041BD_15V	4043BP_5V
4025BD_5V	4028BT_10V	4041BD_5V	4043BT_10V
4025BP_10V	4028BT_15V	4041BP_10V	4043BT_15V
4025BP_15V	4028BT_5V	4041BP_15V	4043BT_5V
4025BP_5V	4030BD_10V	4041BP_5V	4044BD_10V
4025BP_5V	4030BD_15V	4041BP_5V	4044BD_15V
4025BT_10V	4030BD_5V	4041BT_10V	4044BD_5V
4025BT_15V	4030BP_10V	4041BT_15V	4044BP_10V
4025BT_5V	4030BP_15V	4041BT_5V	4044BP_15V
4027BD_10V	4030BP_5V	4042BD_10V	4044BP_5V
4027BD_15V	4030BP_5V	4042BD_15V	4044BP_5V
4027BD_5V	4030BT_10V	4042BD_5V	4044BT_10V
4027BP_10V	4030BT_15V	4042BP_10V	4044BT_15V

Multisim 14.0 Full Components

4044BT_5V	4066BP_15V	4070BD_10V	4072BP_5V
4049BD_10V	4066BP_5V	4070BD_15V	4072BP_5V
4049BD_15V	4066BT_10V	4070BD_5V	4072BT_10V
4049BD_5V	4066BT_15V	4070BP_10V	4072BT_15V
4049BP_10V	4066BT_5V	4070BP_15V	4072BT_5V
4049BP_15V	4068BD_10V	4070BP_5V	4073BD_10V
4049BP_5V	4068BD_15V	4070BP_5V	4073BD_15V
4049BP_5V	4068BD_5V	4070BT_10V	4073BD_5V
4049BT_10V	4068BP_10V	4070BT_15V	4073BP_10V
4049BT_15V	4068BP_15V	4070BT_5V	4073BP_15V
4049BT_5V	4068BP_5V	4071BD_10V	4073BP_5V
4050BD_10V	4068BP_5V	4071BD_15V	4073BP_5V
4050BD_15V	4068BT_10V	4071BD_5V	4073BT_10V
4050BD_5V	4068BT_15V	4071BP_10V	4073BT_15V
4050BP_10V	4068BT_5V	4071BP_15V	4073BT_5V
4050BP_15V	4069BCL_10V	4071BP_5V	4075BD_10V
4050BP_5V	4069BCL_15V	4071BP_5V	4075BD_15V
4050BP_5V	4069BCL_5V	4071BT_10V	4075BD_5V
4050BT_10V	4069BCP_10V	4071BT_15V	4075BP_10V
4050BT_15V	4069BCP_15V	4071BT_5V	4075BP_15V
4050BT_5V	4069BCP_5V	4072BD_10V	4075BP_5V
4066BD_10V	4069BCP_5V	4072BD_15V	4075BP_5V
4066BD_15V	4069BD_10V	4072BD_5V	4075BT_10V
4066BD_5V	4069BD_15V	4072BP_10V	4075BT_15V
4066BP_10V	4069BD_5V	4072BP_15V	4075BT_5V

Multisim 14.0 Full Components

4076BD_10V	4078BP_5V	4085BD_10V	4093BP_5V
4076BD_15V	4078BP_5V	4085BD_15V	4093BP_5V
4076BD_5V	4078BT_10V	4085BD_5V	4093BT_10V
4076BD_5V	4078BT_15V	4085BP_10V	4093BT_15V
4076BP_10V	4078BT_5V	4085BP_15V	4093BT_5V
4076BP_15V	4081BD_10V	4085BP_5V	413990-1
4076BP_5V	4081BD_15V	4085BP_5V	43 mF
4076BT_10V	4081BD_5V	4085BT_10V	[C0805C439KBGAC TU]
4076BT_15V	4081BP_10V	4085BT_15V	43 pF
4076BT_5V	4081BP_15V	4085BT_5V	[C0805C430KBGAC TU]
4077BD_10V	4081BP_5V	4086BD_10V	43 pF
4077BD_15V	4081BP_5V	4086BD_15V	[C1206C430KBGAC TU]
4077BD_5V	4081BT_10V	4086BD_5V	43 pF
4077BP_10V	4081BT_15V	4086BD_5V	[C1210C430KBGAC TU]
4077BP_15V	4081BT_5V	4086BP_10V	43 pF
4077BP_5V	4082BD_10V	4086BP_15V	[C1812C430KBGAC TU]
4077BP_5V	4082BD_15V	4086BP_5V	43 pF
4077BT_10V	4082BD_5V	4086BT_10V	[C1825C430KBGAC TU]
4077BT_15V	4082BP_10V	4086BT_15V	43 pF
4077BT_5V	4082BP_15V	4086BT_5V	[C2220C430KBGAC TU]
4078BD_10V	4082BP_5V	4093BD_10V	43 pF
4078BD_15V	4082BP_5V	4093BD_15V	[C2225C430KBGAC TU]
4078BD_5V	4082BT_10V	4093BD_5V	43 pF
4078BP_10V	4082BT_15V	4093BP_10V	[C2225C430KBGAC TU]
4078BP_15V	4082BT_5V	4093BP_15V	

Multisim 14.0 Full Components

430 pF [C0402C431K1HACT U]	430 pF [C2225C431KBGAC TU]	4508BP_10V	4511BT_15V
		4508BP_15V	4511BT_5V
430 pF [C0402C431K3HACT U]	4502BD_10V	4508BP_5V	4512BD_10V
	4502BD_15V	4508BP_5V	4512BD_15V
430 pF [C0402C431K5HACT U]	4502BD_5V	4508BT_10V	4512BD_5V
	4502BP_10V	4508BT_15V	4512BP_10V
	4502BP_15V	4508BT_5V	4512BP_15V
430 pF [C0603C431K1HACT U]	4502BP_5V	4510BD_10V	4512BP_5V
	4502BP_5V	4510BD_15V	4512BP_5V
430 pF [C0603C431K3HACT U]	4502BT_10V	4510BD_5V	4512BT_10V
	4502BT_15V	4510BP_10V	4512BT_15V
430 pF [C0603C431K5HACT U]	4502BT_5V	4510BP_15V	4512BT_5V
	4503BCL_10V	4510BP_5V	4514BD_10V
430 pF [C1206C431KBGAC TU]	4503BCL_15V	4510BP_5V	4514BD_15V
	4503BCL_5V	4510BT_10V	4514BD_5V
430 pF [C1210C431KBGAC TU]	4503BCP_10V	4510BT_15V	4514BP_10V
	4503BCP_15V	4510BT_5V	4514BP_15V
	4503BCP_5V	4511BD_10V	4514BP_5V
430 pF [C1812C431KBGAC TU]	4503BCP_5V	4511BD_15V	4514BP_5V
	4503BD_10V	4511BD_5V	4514BT_10V
430 pF [C1825C431KBGAC TU]	4503BD_15V	4511BP_10V	4514BT_15V
	4503BD_5V	4511BP_15V	4514BT_5V
430 pF [C2220C431KBGAC TU]	4508BD_10V	4511BP_5V	4515BD_10V
	4508BD_15V	4511BP_5V	4515BD_15V
	4508BD_5V	4511BT_10V	4515BD_5V

Multisim 14.0 Full Components

4515BP_10V	4518BT_15V	4556BP_10V	47 nF [C0402C473K4PACT U]
4515BP_15V	4518BT_5V	4556BP_15V	
4515BP_5V	4520BD_10V	4556BP_5V	47 nF [C0402C473K4RACT U]
4515BP_5V	4520BD_15V	4556BP_5V	
4515BT_10V	4520BD_5V	4556BT_10V	47 nF [C0402C473K8PACT U]
4515BT_15V	4520BP_10V	4556BT_15V	
4515BT_5V	4520BP_15V	4556BT_5V	
4516BD_10V	4520BP_5V	4585BD_15V	47 nF [C0402C473K8RACT U]
4516BD_15V	4520BP_5V	4585BD_5V	
4516BD_5V	4520BT_10V	4585BP_15V	47 nF [C0402C473K9PACT U]
4516BP_10V	4520BT_15V	4585BP_5V	
4516BP_15V	4520BT_5V	4585BT_15V	47 nF [C0402C473K9RACT U]
4516BP_5V	4532BD_10V	4585BT_5V	
4516BP_5V	4532BD_15V	45970-4185	47 nF [C0603C473K1RACT U]
4516BT_10V	4532BD_5V	4-644456-0	
4516BT_15V	4532BP_10V	46765-1001	47 nF [C0603C473K3NAC TU]
4516BT_5V	4532BP_15V	46765-2001	
4518BD_10V	4532BP_5V	47 mF [C0805C479KBGAC TU]	47 nF [C0603C473K3RACT U]
4518BD_15V	4532BP_5V		
4518BD_5V	4532BT_10V	47 mF [C1206C479K1GACT U]	47 nF [C0603C473K4RACT U]
4518BP_10V	4532BT_15V		
4518BP_15V	4532BT_5V	47 nF [C0402C473K3RACT U]	47 nF [C0603C473K5NAC TU]
4518BP_5V	4556BD_10V		
4518BP_5V	4556BD_15V		
4518BT_10V	4556BD_5V		

Multisim 14.0 Full Components

47 nF [C0603C473K5RACT U]	47 nF [C0805F473K4RACT U]	47 nF [C1206C473M5UAC TU]	47 nF [C1210C473K5GACT U]
47 nF [C0603C473K8RACT U]	47 nF [C0805F473K5RACT U]	47 nF [C1206F473K1RACT U]	47 nF [C1210C473K5HACT U]
47 nF [C0603C473M3VAC TU]	47 nF [C1206C473K1HACT U]	47 nF [C1206F473K3RACT U]	47 nF [C1210C473K5RACT U]
47 nF [C0805C473K1RACT U]	47 nF [C1206C473K1RACT U]	47 nF [C1206F473K4RACT U]	47 nF [C1210C473KARACT U]
47 nF [C0805C473K3RACT U]	47 nF [C1206C473K3GACT U]	47 nF [C1206F473K5RACT U]	47 nF [C1812C473K1GACT U]
47 nF [C0805C473K4RACT U]	47 nF [C1206C473K3HACT U]	47 nF [C1210C473K1GACT U]	47 nF [C1812C473K1HACT U]
47 nF [C0805C473K5RACT U]	47 nF [C1206C473K3RACT U]	47 nF [C1210C473K1HACT U]	47 nF [C1812C473K1RACT U]
47 nF [C0805C473K8RACT U]	47 nF [C1206C473K4RACT U]	47 nF [C1210C473K1RACT U]	47 nF [C1812C473K2RACT U]
47 nF [C0805C473M5UAC TU]	47 nF [C1206C473K5HACT U]	47 nF [C1210C473K2RACT U]	47 nF [C1812C473K5GACT U]
47 nF [C0805C473M5VAC TU]	47 nF [C1206C473K5RACT U]	47 nF [C1210C473K3GACT U]	47 nF [C1812C473K5HACT U]
47 nF [C0805F473K3RACT U]	47 nF [C1206C473KARACT U]	47 nF [C1210C473K3HACT U]	47 nF [C1812C473K5RACT U]

Multisim 14.0 Full Components

47 nF [C1825C473K5RACT U]	47 pF [C0603C470K1GACT U]	47 pF [C1206C470K3GACT U]	47 pF [C2220C470KBGAC TU]
47 nF [C2220C473K1GACT U]	47 pF [C0603C470K5GACT U]	47 pF [C1206C470K5GACT U]	47 pF [C2225C470KBGAC TU]
47 nF [C2220C473K2GACT U]	47 pF [C0603C470K8GACT U]	47 pF [C1206C470KBGAC TU]	47 pF [CA064C470K3GAC TU]
47 nF [C2220C473K5GACT U]	47 pF [C0805C470K1GACT U]	47 pF [C1206C470KDGAC TU]	47 pF [CA064C470K5GAC TU]
47 nF [CA064C473K4RACT U]	47 pF [C0805C470K2GACT U]	47 pF [C1206C470KFGACT U]	47 pF [CA064C470K8GAC TU]
47 nF [CA064C473K8RACT U]	47 pF [C0805C470K3GACT U]	47 pF [C1206C470KGGAC TU]	47 uF [A700V476M006AT E018]
47 pF [C0201C470K3GACT U]	47 pF [C0805C470K5GACT U]	47 pF [C1210C470K5GACT U]	47 uF [A700V476M006AT E025]
47 pF [C0402C470K3GACT U]	47 pF [C0805C470KBGAC TU]	47 pF [C1210C470KBGAC TU]	47 uF [A700V476M006AT E028]
47 pF [C0402C470K4GACT U]	47 pF [C0805C470KCGAC TU]	47 pF [C1812C470KBGAC TU]	47 uF [T409H476M010AH 4250]
47 pF [C0402C470K5GACT U]	47 pF [C1206C470K1GACT U]	47 pF [C1812C470KDGAC TU]	47 uF [T419F476M010AH 4250]
47 pF [C0402C470K8GACT U]	47 pF [C1206C470K2GACT U]	47 pF [C1825C470KBGAC TU]	47 uF [T491A476M004AT] 47 uF [T491A476M006AT]

Multisim 14.0 Full Components

47 uF [T491B476M004AT]	47 uF [T491E476M035AT]	47 uF [T494B476M010AT]	47 uF [T494T476M006AT]
47 uF [T491B476M006AT]	47 uF [T491T476M004AT]	47 uF [T494C476M004AT]	47 uF [T494U476M004AT]
47 uF [T491B476M010AT]	47 uF [T491T476M006AT]	47 uF [T494C476M006AT]	47 uF [T494U476M006AT]
47 uF [T491C476M004AT]	47 uF [T491U476M004AT]	47 uF [T494C476M010AT]	47 uF [T494U476M010AT]
47 uF [T491C476M006AT]	47 uF [T491U476M006AT]	47 uF [T494C476M016AT]	47 uF [T494V476M010AT]
47 uF [T491C476M010AT]	47 uF [T491U476M010AT]	47 uF [T494C476M020AT]	47 uF [T494V476M016AT]
47 uF [T491C476M016AT]	47 uF [T491V476M010AT]	47 uF [T494D476M006AT]	47 uF [T494X476M025AT]
47 uF [T491C476M020AT]	47 uF [T491V476M016AT]	47 uF [T494D476M010AT]	47 uF [T494X476M035AT]
47 uF [T491D476M006AT]	47 uF [T491X476M025AT]	47 uF [T494D476M016AT]	47 uF [T495B476M006AT E450]
47 uF [T491D476M010AT]	47 uF [T491X476M035AT]	47 uF [T494D476M020AT]	47 uF [T495B476M010AT E500]
47 uF [T491D476M016AT]	47 uF [T494A476M004AT]	47 uF [T494D476M025AT]	47 uF [T495C476M016AT E350]
47 uF [T491D476M020AT]	47 uF [T494A476M006AT]	47 uF [T494E476M035AT]	47 uF [T495D476M010AT E080]
47 uF [T491D476M025AT]	47 uF [T494B476M004AT]	47 uF [T494T476M004AT]	
	47 uF [T494B476M006AT]		

Multisim 14.0 Full Components

47 uF [T495D476M010AT E090]	47 uF [T495X476M020AT E100]	47 uF [T498D476M010AT E600]	47 uF [T520B476M006AT E040]
47 uF [T495D476M010AT E200]	47 uF [T495X476M020AT E150]	47 uF [T498D476M016AT E600]	47 uF [T520B476M006AT E070]
47 uF [T495D476M016AT E080]	47 uF [T495X476M025AT E080]	47 uF [T510E476M035AT E050]	47 uF [T520B476M008AT E035]
47 uF [T495D476M016AT E100]	47 uF [T495X476M025AT E150]	47 uF [T510X476M035AT E055]	47 uF [T520B476M008AT E070]
47 uF [T495D476M016AT E150]	47 uF [T495X476M025AT E185]	47 uF [T510X476M035AT E065]	47 uF [T520B476M010AT E035]
47 uF [T495D476M020AT E100]	47 uF [T495X476M025AT E200]	47 uF [T520A476M004AT E070]	47 uF [T520B476M010AT E070]
47 uF [T495D476M020AT E175]	47 uF [T495X476M035AT E185]	47 uF [T520A476M004AT E080]	47 uF [T520C476M010AT E100]
47 uF [T495D476M025AT E120]	47 uF [T495X476M035AT E200]	47 uF [T520A476M006AT E150]	47 uF [T520D476M016AT E035]
47 uF [T495D476M025AT E250]	47 uF [T495X476M035AT E300]	47 uF [T520A476M2R5AT E090]	47 uF [T520D476M016AT E070]
47 uF [T495V476M006AT E150]	47 uF [T497G476M006AT 6110]	47 uF [T520B476M006AT E025]	47 uF [T520Q476M011AT E040]
47 uF [T495X476M020AT E065]	47 uF [T498C476M006AT E800]	47 uF [T520B476M006AT E035]	47 uF [T520T476M004AT E070]

Multisim 14.0 Full Components

47 uF [T520T476M006AT E040]	47 uF [T525D476M016AT E035]	470 nF [C0603C474K9RACT U]	470 nF [C1206C474K5NAC TU]
47 uF [T520T476M006AT E070]	47 uF [T525D476M016AT E065]	470 nF [C0805C474K3NAC TU]	470 nF [C1206C474K5RACT U]
47 uF [T520V476M016AT E045]	47 uF [T525T476M006AT E080]	470 nF [C0805C474K3PACT U]	470 nF [C1206C474K8RACT U]
47 uF [T520V476M016AT E070]	47 uF [T543A476M004AT E080]	470 nF [C0805C474K3RACT U]	470 nF [C1206C474M3VAC TU]
47 uF [T520W476M016AT E045]	47 uF [T543W476M016AT E045]	470 nF [C0805C474K4RACT U]	470 nF [C1206C474M4VAC TU]
47 uF [T521D476M020AT E055]	470 nF [C0402C474K9PACT U]	470 nF [C0805C474K8RACT U]	470 nF [C1206F474K3RACT U]
47 uF [T521V476M020AT E090]	470 nF [C0603C474K4PACT U]	470 nF [C0805C474M3VAC TU]	470 nF [C1206F474K4RACT U]
47 uF [T521W476M020AT E045]	470 nF [C0603C474K4RACT U]	470 nF [C0805C474M4VAC TU]	470 nF [C1210C474K3RACT U]
47 uF [T521X476M035AT E030]	470 nF [C0603C474K8PACT U]	470 nF [C1206C474K3NAC TU]	470 nF [C1210C474K4RACT U]
47 uF [T521X476M035AT E070]	470 nF [C0603C474K8RACT U]	470 nF [C1206C474K3RACT U]	470 nF [C1210C474K5RACT U]
47 uF [T525B476M006AT E080]	470 nF [C0603C474K9PACT U]	470 nF [C1206C474K4RACT U]	470 nF [C1210C474M5UAC TU]

Multisim 14.0 Full Components

470 nF [C1210F474K1RACT U]	470 nF [C1825C474K5RACT U]	470 nF [T491A474M025AT]	470 pF [C0402C471K3RACT U]
470 nF [C1210F474K3RACT U]	470 nF [C1825C474KARACT U]	470 nF [T491A474M035AT]	470 pF [C0402C471K4RACT U]
470 nF [C1210F474K4RACT U]	470 nF [C2220C474K1RACT U]	470 nF [T491B474M035AT]	470 pF [C0402C471K5HACT U]
470 nF [C1210F474K5RACT U]	470 nF [C2220C474K5RACT U]	470 nF [T491C474M050AT]	470 pF [C0402C471K5RACT U]
470 nF [C1812C474K5RACT U]	470 nF [C2220C474KARACT U]	470 nF [T494A474M025AT]	470 pF [C0402C471K8RACT U]
470 nF [C1812C474KARACT U]	470 nF [C2225C474K1RACT U]	470 nF [T494B474M035AT]	470 pF [C0402C471K9RACT U]
470 nF [C1812C474M5UAC TU]	470 nF [C2225C474K2RACT U]	470 nF [T494B474M050AT]	470 pF [C0603C471K1HACT U]
470 nF [C1812F474K1RACT U]	470 nF [C2225C474K5RACT U]	470 nF [T494C474M050AT]	470 pF [C0603C471K1RACT U]
470 nF [C1812F474K3RACT U]	470 nF [C2225C474KARACT U]	470 nF [T498A474M025AT E8K5]	470 pF [C0603C471K2RACT U]
470 nF [C1812F474K5RACT U]	470 nF [C2225C474M1UAC TU]	470 pF [C0402C471K1HACT U]	470 pF [C0603C471K3GACT U]
470 nF [C1825C474K1RACT U]	470 nF [CDR06BX474AKSM]	470 pF [C0402C471K3HACT U]	470 pF [C0603C471K3HACT U]

Multisim 14.0 Full Components

470 pF [C0603C471K3RACT U]	470 pF [C0805C471K4RACT U]	470 pF [C1210C471KCGAC TU]	470 uF [A700X477M002AT E010]
470 pF [C0603C471K4RACT U]	470 pF [C0805C471K5GACT U]	470 pF [C1812C471K5GACT U]	470 uF [A700X477M002AT E015]
470 pF [C0603C471K5GACT U]	470 pF [C0805C471K5RACT U]	470 pF [C1812C471KBGAC TU]	470 uF [T489X477M006AT E200]
470 pF [C0603C471K5HACT U]	470 pF [C0805C471KARACT U]	470 pF [C1825C471KBGAC TU]	470 uF [T491D477M004AT]
470 pF [C0603C471K5RACT U]	470 pF [C1206C471K1GACT U]	470 pF [C2220C471KBGAC TU]	470 uF [T491D477M006AT]
470 pF [C0603C471K8RACT U]	470 pF [C1206C471K2GACT U]	470 pF [C2225C471KBGAC TU]	470 uF [T491E477M006AT]
470 pF [C0805C471K1GACT U]	470 pF [C1206C471K5GACT U]	470 pF [CA064C471K4RACT U]	470 uF [T491E477M010AT]
470 pF [C0805C471K1RACT U]	470 pF [C1206C471KBGAC TU]	470 pF [CA064C471K5GAC TU]	470 uF [T491X477M004AT]
470 pF [C0805C471K2GACT U]	470 pF [C1206C471KCGAC TU]	470 pF [CA064C471K5RACT U]	470 uF [T491E477M006AT]
470 pF [C0805C471K2RACT U]	470 pF [C1210C471K5GACT U]	470 pF [CA064C471K8RAC]	470 uF [T491X477M010AT]
470 pF [C0805C471K3RACT U]	470 pF [C1210C471KBGAC TU]	470 uF [A700X477M002AT E007]	470 uF [T494D477M006AT]
			470 uF [T494E477M006AT]

Multisim 14.0 Full Components

470 uF [T494E477M010AT]	470 uF [T495X477M006AT E045]	470 uF [T520C477M2R5AT E045]	470 uF [T520D477M2R5AT E009]
470 uF [T494X477M004AT]	470 uF [T495X477M006AT E050]	470 uF [T520D477M004AT E010]	470 uF [T520V477M002AT E040]
470 uF [T494X477M006AT]			
470 uF [T494X477M010AT]	470 uF [T495X477M006AT E065]	470 uF [T520D477M004AT E012]	470 uF [T520V477M2R5AT E007]
470 uF [T495D477M006AT E045]	470 uF [T495X477M010AT E045]	470 uF [T520D477M004AT E015]	470 uF [T520V477M2R5AT E009]
470 uF [T495D477M006AT E100]	470 uF [T495X477M010AT E050]	470 uF [T520D477M004AT E018]	470 uF [T520V477M2R5AT E012]
470 uF [T495D477M006AT E125]	470 uF [T495X477M010AT E060]	470 uF [T520D477M004AT E025]	470 uF [T520V477M2R5AT E015]
470 uF [T495E477M006AT E040]	470 uF [T495X477M010AT E100]	470 uF [T520D477M004AT E040]	470 uF [T520V477M2R5AT E018]
470 uF [T495X477M004AT E030]	470 uF [T495X477M010AT E200]	470 uF [T520D477M006AT E025]	470 uF [T520W477M006AT E055]
470 uF [T495X477M004AT E045]	470 uF [T510X477M006AT E030]	470 uF [T520D477M006AT E030]	470 uF [T520X477M006AT E010]
470 uF [T495X477M004AT E100]	470 uF [T513X477M006AH 6110]	470 uF [T520D477M2R5AT E006]	470 uF [T520X477M006AT E018]
470 uF [T495X477M006AT E030]	470 uF [T520C477M2R5AT E025]	470 uF [T520D477M2R5AT E007]	470 uF [T520X477M006AT E035]

Multisim 14.0 Full Components

470 uF [T520X477M006AT E040]	470 uF [T528Z477M2R5AT E009]	470 uF [T543D477M2R5AT E007]	5.1 nF [C2220C512KBGAC TU]
470 uF [T520Y477M006AT E010]	470 uF [T528Z477M2R5AT E012]	47151-0001 47272-0001	5.1 nF [C2225C512KBGAC TU]
470 uF [T520Y477M006AT E015]	470 uF [T530D477M004AT E006]	4Line_Bussed 4Line_Isolated 4Line_Terminator	5.6 nF [C0402C562K3RACT U]
470 uF [T520Y477M006AT E018]	470 uF [T530D477M004AT E010]	4POS_ROTARY 4V_0.5W	5.6 nF [C0402C562K4RACT U]
470 uF [T520Y477M006AT E025]	470 uF [T530D477M2R5AT E006]	5.1 nF [C0603C512K3HACT U]	5.6 nF [C0402C562K5RACT U]
470 uF [T522Y477M006AT E040]	470 uF [T530X477M006AT E004]	5.1 nF [C0603C512K5HACT U]	5.6 nF [C0603C562K1RACT U]
470 uF [T525D477M003AT E025]	470 uF [T530X477M006AT E005]	5.1 nF [C0805C512K1GACT U]	5.6 nF [C0603C562K3GACT U]
470 uF [T525D477M004AT E025]	470 uF [T530X477M006AT E006]	5.1 nF [C0805C512K1HACT U]	5.6 nF [C0603C562K3HACT U]
470 uF [T525D477M004AT E040]	470 uF [T530X477M006AT E010]	5.1 nF [C0805C512K3HACT U]	5.6 nF [C0603C562K3RACT U]
470 uF [T525D477M2R5AT E025]	470 uF [T530Y477M004AT E005]	5.1 nF [C0805C512K5HACT U]	5.6 nF [C0603C562K4RACT U]
470 uF [T528Z477M2R5AT E005]	470 uF [T530Y477M006AT E005]	5.1 nF [C1206C512K5GACT U]	5.6 nF [C0603C562K5HACT U]

Multisim 14.0 Full Components

5.6 nF [C0603C562K5RACT U]	5.6 nF [C0805C562K5RACT U]	5.6 nF [C2220C562KBGAC TU]	51 pF [C0402C510K5GACT U]
5.6 nF [C0603C562K8RACT U]	5.6 nF [C0805C562KARACT U]	5.6 nF [C2225C562KBGAC TU]	51 pF [C0603C510K2GACT U]
5.6 nF [C0805C562K1GACT U]	5.6 nF [C1206C562K1RACT U]	5.6 uF [C0805C565K9PACT U]	51 pF [C0603C510K5GACT U]
5.6 nF [C0805C562K1HACT U]	5.6 nF [C1206C562K2RACT U]	5.6 uF [C1206C565K4RACT U]	51 pF [C0805C510K1GACT U]
5.6 nF [C0805C562K1RACT U]	5.6 nF [C1206C562K5GACT U]	5.6 uF [C1206C565K8RACT U]	51 pF [C0805C510K2GACT U]
5.6 nF [C0805C562K2RACT U]	5.6 nF [C1206C562K5RACT U]	5.6 uF [C1206C565K9RACT U]	51 pF [C0805C510K5GACT U]
5.6 nF [C0805C562K3GACT U]	5.6 nF [C1206C562KARACT U]	5.6 uF [C1210C565K4PACT U]	51 pF [C0805C510KBGAC TU]
5.6 nF [C0805C562K3HACT U]	5.6 nF [C1210C562K5GACT U]	5 AMP 50 AMP	51 pF [C0805C510KCGAC TU]
5.6 nF [C0805C562K3RACT U]	5.6 nF [C1210C562K5RACT U]	50A02CH-TL-E 50A02CH-TL-H	51 pF [C1206C510K5GACT U]
5.6 nF [C0805C562K4RACT U]	5.6 nF [C1210C562KARACT U]	50C02CH-TL-E	51 pF [C1206C510KBGAC TU]
5.6 nF [C0805C562K5HACT U]	5.6 nF [C1812C562K2GACT U]	51 mF [C0805C519K3GACT U]	51 pF [C1210C510KBGAC TU]
		51 mF [C0805C519KBGAC TU]	

Multisim 14.0 Full Components

51 pF [C1812C510KBGAC TU]	510 pF [C0603C511K8GACT U]	5103310-1 5103310-5 5103310-6 5103310-7 5103310-8	56 nF [C0402C563K9RACT U]
51 pF [C1825C510KBGAC TU]	510 pF [C0805C511K5GACT U]	5-1814400-1 5227222-3	56 nF [C0603C563K3RACT U]
51 pF [C2220C510KBGAC TU]	510 pF [C1206C511K1GACT U]	5227677-1 532903-2	56 nF [C0603C563K5RACT U]
51 pF [C2225C510KBGAC TU]	510 pF [C1206C511KBGAC TU]	532903-6 534206-5	56 nF [C0805C563K1RACT U]
510 pF [C0402C511K1HACT U]	510 pF [C1210C511KBGAC TU]	534237-3 534237-6	56 nF [C0805C563K2RACT U]
510 pF [C0402C511K3HACT U]	510 pF [C1812C511KBGAC TU]	534237-8 5414337-1	56 nF [C0805C563K3RACT U]
510 pF [C0402C511K5HACT U]	510 pF [C1825C511KBGAC TU]	555_TIMER_RATED	56 nF [C0805C563K4RACT U]
510 pF [C0603C511K1HACT U]	510 pF [C2220C511KBGAC TU]	555_VIRTUAL 5558067-1	56 nF [C0805C563K5RACT U]
510 pF [C0603C511K3HACT U]	510 pF [C2225C511KBGAC TU]	56 mF [C0805C569KBGAC TU]	56 nF [C0805C563K8RACT U]
510 pF [C0603C511K5GACT U]	5103309-1 5103309-5 5103309-6 5103309-7 5103309-8	56 nF [C0402C563K4RACT U]	56 nF [C0805F563K3RACT U]

Multisim 14.0 Full Components

56 nF [C0805F563K4RACT U]	56 nF [C1206F563K4RACT U]	56 nF [C1812C563K1GACT U]	56 pF [C0402C560K5GACT U]
56 nF [C0805F563K5RACT U]	56 nF [C1206F563K5RACT U]	56 nF [C1812C563K1HACT U]	56 pF [C0402C560K8GACT U]
56 nF [C1206C563K1RACT U]	56 nF [C1210C563K1GACT U]	56 nF [C1812C563K1RACT U]	56 pF [C0603C560K1GACT U]
56 nF [C1206C563K3HACT U]	56 nF [C1210C563K1HACT U]	56 nF [C1812C563K5GACT U]	56 pF [C0603C560K2GACT U]
56 nF [C1206C563K3RACT U]	56 nF [C1210C563K1RACT U]	56 nF [C1812C563K5HACT U]	56 pF [C0603C560K3GACT U]
56 nF [C1206C563K5HACT U]	56 nF [C1210C563K2RACT U]	56 nF [C2220C563K1GACT U]	56 pF [C0603C560K5GACT U]
56 nF [C1206C563K5RACT U]	56 nF [C1210C563K3HACT U]	56 nF [C2220C563K2GACT U]	56 pF [C0805C560K1GACT U]
56 nF [C1206C563KARACT U]	56 nF [C1210C563K5GACT U]	56 nF [C2220C563K5GACT U]	56 pF [C0805C560K2GACT U]
56 nF [C1206C563M5UAC TU]	56 nF [C1210C563K5HACT U]	56 pF [C0201C560K3GACT U]	56 pF [C0805C560K5GACT U]
56 nF [C1206F563K1RACT U]	56 nF [C1210C563K5RACT U]	56 pF [C0201C560K8GACT U]	56 pF [C0805C560KBGAC TU]
56 nF [C1206F563K3RACT U]	56 nF [C1210C563KARACT U]	56 pF [C0402C560K3GACT U]	56 pF [C0805C560KDGAC TU]

Multisim 14.0 Full Components

56 pF [C1206C560K1GACT U]	56 pF [CA064C560K5GAC TU]	560 nF [C0805C564K3RACT U]	560 nF [C1812C564K5RACT U]
56 pF [C1206C560K2GACT U]	56 uF [A700D566M008AT E015]	560 nF [C0805C564K4RACT U]	560 nF [C1812F564K1RACT U]
56 pF [C1206C560K5GACT U]	56 uF [A700D566M008AT E018]	560 nF [C0805C564K8RACT U]	560 nF [C1812F564K3RACT U]
56 pF [C1206C560KBGAC TU]	56 uF [A700D566M010AT E015]	560 nF [C1206C564K3RACT U]	560 nF [C1812F564K5RACT U]
56 pF [C1206C560KDGAC TU]	56 uF [A700D566M010AT E018]	560 nF [C1206C564K4RACT U]	560 nF [C1825C564K5RACT U]
56 pF [C1210C560KBGAC TU]	56 uF [A700V566M006AT E018]	560 nF [C1206C564K5RACT U]	560 nF [C1825C564KARACT U]
56 pF [C1812C560KBGAC TU]	56 uF [A700V566M006AT E025]	560 nF [C1206F564K4RACT U]	560 nF [C2220C564K1RACT U]
56 pF [C1812C560KHGAC TU]	56 uF [A700V566M006AT E028]	560 nF [C1210C564K5RACT U]	560 nF [C2220C564K5RACT U]
56 pF [C1825C560KBGAC TU]	56 uF [T520T566M2R5AT E040]	560 nF [C1210F564K3RACT U]	560 nF [C2220C564KARACT U]
56 pF [C2220C560KBGAC TU]	56 uF [T520T566M2R5AT E070]	560 nF [C1210F564K4RACT U]	560 nF [C2225C564K5RACT U]
56 pF [C2225C560KBGAC TU]	560 nF [C0603C564K8PACT U]	560 nF [C1210F564K5RACT U]	560 nF [C2225C564KARACT U]

Multisim 14.0 Full Components

560 pF [C0402C561K1HACT U]	560 pF [C0603C561K3HACT U]	560 pF [C0805C561K5GACT U]	560 pF [C2225C561KBGAC TU]
560 pF [C0402C561K3GACT U]	560 pF [C0603C561K3RACT U]	560 pF [C0805C561K5RACT U]	560 pF [CA064C561K2RACT U]
560 pF [C0402C561K3HACT U]	560 pF [C0603C561K4RACT U]	560 pF [C0805C561K8RACT U]	560 uF [T530D567M2R5AT E005]
560 pF [C0402C561K3RACT U]	560 pF [C0603C561K5GACT U]	560 pF [C1206C561K1GACT U]	5687169-9
560 pF [C0402C561K4RACT U]	560 pF [C0603C561K5HACT U]	560 pF [C1206C561K2GACT U]	571-0100
560 pF [C0402C561K5HACT U]	560 pF [C0603C561K5RACT U]	560 pF [C1206C561K5GACT U]	571-0200
560 pF [C0402C561K5RACT U]	560 pF [C0603C561K8RACT U]	560 pF [C1206C561KBGAC TU]	571-0300
560 pF [C0402C561K8RACT U]	560 pF [C0805C561K1GACT U]	560 pF [C1210C561KBGAC TU]	571-0400
560 pF [C0603C561K1HACT U]	560 pF [C0805C561K1RACT U]	560 pF [C1812C561KBGAC TU]	571-0500
560 pF [C0603C561K1RACT U]	560 pF [C0805C561K2RACT U]	560 pF [C1825C561KBGAC TU]	571-0600
560 pF [C0603C561K2RACT U]	560 pF [C0805C561K4RACT U]	560 pF [C2220C561KBGAC TU]	571-0700
			5KP10A-E3/54
			5KP16A-E3/54
			5KP18A-E3/54
			5KP22A-E3/54
			5KP24A-E3/54
			5KP28A-E3/54
			5KP30A-E3/54
			5KP33A-E3/54
			5KP40A-E3/54
			5KP48A-E3/54

Multisim 14.0 Full Components

5KP58A-E3/54	6.2 nF [C0805C622K3HACT U]	6.8 nF [C0603C682K3RACT U]	6.8 nF [C0805C682K4RACT U]
5KP60A-E3/54			
5KP85A-E3/54	6.2 nF [C0805C622K5HACT U]	6.8 nF [C0603C682K4RACT U]	6.8 nF [C0805C682K5GACT U]
5Line_Bussed			
5Line_Isolated	6.2 nF [C2225C622KBGAC TU]	6.8 nF [C0603C682K5HACT U]	6.8 nF [C0805C682K5HACT U]
5LN01C-TB-E			
5LN01C-TB-H	6.8 nF [C0402C682K3RACT U]	6.8 nF [C0603C682K5RACT U]	6.8 nF [C0805C682K5RACT U]
5LN01M-TL-E			
5LN01M-TL-H	6.8 nF [C0402C682K4RACT U]	6.8 nF [C0603C682K8RACT U]	6.8 nF [C1206C682K1HACT U]
5LN01SP-AC			
5LN01SS-TL-E	6.8 nF [C0402C682K5RACT U]	6.8 nF [C0805C682K1GACT U]	6.8 nF [C1206C682K1RACT U]
5LN01SS-TL-H			
5LN01S-TL-E	6.8 nF [C0402C682K8RACT U]	6.8 nF [C0805C682K1HACT U]	6.8 nF [C1206C682K3GACT U]
5POS_ROTARY			
5V_1W	6.2 nF [C0603C622K3HACT U]	6.8 nF [C0603C682K1RACT U]	6.8 nF [C1206C682K3HACT U]
6.2 nF [C0603C622K5HACT U]	6.8 nF [C0603C682K2RACT U]	6.8 nF [C0805C682K3GACT U]	6.8 nF [C1206C682K3RACT U]
6.2 nF [C0805C622K1GACT U]	6.8 nF [C0603C682K3GACT U]	6.8 nF [C0805C682K3HACT U]	6.8 nF [C1206C682K5HACT U]
6.2 nF [C0805C622K1HACT U]	6.8 nF [C0603C682K3HACT U]	6.8 nF [C0805C682K3RACT U]	6.8 nF [C1206C682K5RACT U]

Multisim 14.0 Full Components

6.8 nF [C1210C682K1GACT U]	6.8 nF [CDR06BP682BKSM]	6.8 uF [C1210C685K8PACT U]	6.8 uF [T491B685M016AT]
6.8 nF [C1210C682K1RACT U]	6.8 uF [A700V685M016AT E070]	6.8 uF [C1210C685M4VAC TU]	6.8 uF [T491B685M025AT]
6.8 nF [C1210C682K5GACT U]	6.8 uF [C0805C685K8PACT U]	6.8 uF [T419B685M006AH 4250]	6.8 uF [T491C685M016AT]
6.8 nF [C1210C682K5RACT U]	6.8 uF [C0805C685K9PACT U]	6.8 uF [T419C685M010AH 4250]	6.8 uF [T491C685M025AT]
6.8 nF [C1210C682KARACT U]	6.8 uF [C1206C685K4PACT U]	6.8 uF [T429D685M006AH 4250]	6.8 uF [T491C685M035AT]
6.8 nF [C1812C682K1GACT U]	6.8 uF [C1206C685K4RACT U]	6.8 uF [T489B685M010AT E3K0]	6.8 uF [T491D685M050AT]
6.8 nF [C1812C682K1RACT U]	6.8 uF [C1206C685K8RACT U]	6.8 uF [T491A685M004AT]	6.8 uF [T491S685M004AT]
6.8 nF [C1812C682K5GACT U]	6.8 uF [C1206C685K9PACT U]	6.8 uF [T491A685M006AT]	6.8 uF [T491S685M006AT]
6.8 nF [C1812C682K5RACT U]	6.8 uF [C1206C685K9RACT U]	6.8 uF [T491A685M010AT]	6.8 uF [T491S685M010AT]
6.8 nF [C2220C682K2GACT U]	6.8 uF [C1210C685K3PACT U]	6.8 uF [T491A685M020AT]	6.8 uF [T491U685M020AT]
6.8 nF [C2225C682KBGAC TU]	6.8 uF [C1210C685K4PACT U]	6.8 uF [T491B685M006AT]	6.8 uF [T491X685M050AT]

Multisim 14.0 Full Components

6.8 uF [T494A685M004AT]	6.8 uF [T494D685M050AT]	6.8 uF [T495D685M050AT E300]	62 pF [C0603C620K5GACT U]
6.8 uF [T494A685M006AT]	6.8 uF [T494S685M004AT]	6.8 uF [T497B685M010AT 6110]	62 pF [C0805C620KBGAC TU]
6.8 uF [T494A685M010AT]	6.8 uF [T494S685M006AT]	6.8 uF [T498A685M016AT E2K6]	62 pF [C1206C620KBGAC TU]
6.8 uF [T494A685M016AT]	6.8 uF [T494S685M010AT]	6.8 uF [T498B685M016AT E1K8]	62 pF [C1206C620KDGAC TU]
6.8 uF [T494A685M020AT]	6.8 uF [T494T685M010AT]	6.8 uF [T498D685M035AT E900]	62 pF [C1210C620KBGAC TU]
6.8 uF [T494B685M006AT]	6.8 uF [T494U685M020AT]	6.8 uF [T499C685M020AT E1K9]	62 pF [C1812C620KBGAC TU]
6.8 uF [T494B685M010AT]	6.8 uF [T494X685M050AT]	6.8 uF [T521D685M050AT E090]	62 pF [C1825C620KBGAC TU]
6.8 uF [T494B685M016AT]	6.8 uF [T495C685M025AT E400]	6.8 uF [T521V685M050AT E090]	62 pF [C2220C620KBGAC TU]
6.8 uF [T494B685M020AT]	6.8 uF [T495C685M025AT E500]	61729-0010BLF	62 pF [C2225C620KBGAC TU]
6.8 uF [T494B685M025AT]	6.8 uF [T495D685M035AT E150]	62 mF [C0805C629KBGAC TU]	620 pF [C0402C621K1HACT U]
6.8 uF [T494C685M016AT]	6.8 uF [T495D685M050AT E190]	62 pF [C0402C620K3GACT U]	620 pF [C0402C621K3HACT U]
6.8 uF [T494C685M020AT]	6.8 uF [T495D685M050AT E200]	62 pF [C0402C620K5GACT U]	
6.8 uF [T494C685M025AT]			
6.8 uF [T494C685M035AT]			
6.8 uF [T494D685M035AT]			

Multisim 14.0 Full Components

620 pF [C0402C621K5HACT U]	640455-8 68 mF [C0402C689K8GACT U]	68 nF [C0603C683K8RACT U]	68 nF [C0805F683K5RACT U]
620 pF [C0603C621K1HACT U]	68 mF [C0805C689KBGAC TU]	68 nF [C0603C683K9RACT U]	68 nF [C1206C683K1RACT U]
620 pF [C0603C621K3HACT U]	68 mF [C1206C689K2GACT U]	68 nF [C0603C683M3VAC TU]	68 nF [C1206C683K2RACT U]
620 pF [C0603C621K5GACT U]	68 nF [C0402C683K4RACT U]	68 nF [C0805C683K1RACT U]	68 nF [C1206C683K3GACT U]
620 pF [C0603C621K5HACT U]	68 nF [C0402C683K8PACT U]	68 nF [C0805C683K3RACT U]	68 nF [C1206C683K3HACT U]
620 pF [C0805C621K5GACT U]	68 nF [C0402C683K8RACT U]	68 nF [C0805C683K4RACT U]	68 nF [C1206C683K5HACT U]
620 pF [C1210C621KBGAC TU]	68 nF [C0402C683K9PACT U]	68 nF [C0805C683K5RACT U]	68 nF [C1206C683K5RACT U]
620 pF [C1812C621KBGAC TU]	68 nF [C0402C683K9RACT U]	68 nF [C0805C683K8RACT U]	68 nF [C1206C683KARACT U]
620 pF [C1825C621KBGAC TU]	68 nF [C0603C683K3RACT U]	68 nF [C0805C683M5UAC TU]	68 nF [C1206C683M5UAC TU]
620 pF [C2220C621KBGAC TU]	68 nF [C0603C683K4RACT U]	68 nF [C0805F683K3RACT U]	68 nF [C1206F683K1RACT U]
620 pF [C2225C621KBGAC TU]	68 nF [C0603C683K5RACT U]	68 nF [C0805F683K4RACT U]	68 nF [C1206F683K3RACT U]
640455-5			

Multisim 14.0 Full Components

68 nF [C1206F683K4RACT U]	68 nF [C1210C683KARACT U]	68 nF [C2220C683K5GACT U]	68 pF [C0805C680K1GACT U]
68 nF [C1206F683K5RACT U]	68 nF [C1210F683K2RACT U]	68 nF [CA064C683K4RACT U]	68 pF [C0805C680K2GACT U]
68 nF [C1210C683K1GACT U]	68 nF [C1812C683K1GACT U]	68 nF [CDR05BX683BKSM]	68 pF [C0805C680K5GACT U]
68 nF [C1210C683K1HACT U]	68 nF [C1812C683K1HACT U]	68 pF [C0201C680K3GACT U]	68 pF [C0805C680KBGAC TU]
68 nF [C1210C683K1RACT U]	68 nF [C1812C683K1RACT U]	68 pF [C0402C680K3GACT U]	68 pF [C1206C680K1GACT U]
68 nF [C1210C683K2RACT U]	68 nF [C1812C683K2RACT U]	68 pF [C0402C680K5GACT U]	68 pF [C1206C680K2GACT U]
68 nF [C1210C683K3GACT U]	68 nF [C1812C683K5GACT U]	68 pF [C0402C680K8GACT U]	68 pF [C1206C680K5GACT U]
68 nF [C1210C683K3HACT U]	68 nF [C1812C683K5HACT U]	68 pF [C0603C680K2GACT U]	68 pF [C1206C680KBGAC TU]
68 nF [C1210C683K5GACT U]	68 nF [C1812C683K5RACT U]	68 pF [C0603C680K3GACT U]	68 pF [C1206C680KDGAC TU]
68 nF [C1210C683K5HACT U]	68 nF [C2220C683K1GACT U]	68 pF [C0603C680K4GACT U]	68 pF [C1206C680KGGAC TU]
68 nF [C1210C683K5RACT U]	68 nF [C2220C683K2GACT U]	68 pF [C0603C680K5GACT U]	68 pF [C1210C680KBGAC TU]

Multisim 14.0 Full Components

68 pF [C1812C680KBGAC TU]	68 uF [A700V686M006AT E018]	68 uF [T491D686M004AT]	68 uF [T491X686M025AT]
68 pF [C1825C680KBGAC TU]	68 uF [A700V686M006AT E025]	68 uF [T491D686M006AT]	68 uF [T494A686M004AT]
68 pF [C2220C680KBGAC TU]	68 uF [A700V686M006AT E028]	68 uF [T491D686M010AT]	68 uF [T494B686M004AT]
68 pF [C2225C680KBGAC TU]	68 uF [T419G686M010AH 4250]	68 uF [T491D686M016AT]	68 uF [T494B686M006AT]
68 pF [CA064C680K5GAC TU]	68 uF [T491A686M004AT]	68 uF [T491D686M020AT]	68 uF [T494B686M010AT]
68 pF [CA064C680K8GAC TU]	68 uF [T491A686M006AT]	68 uF [T491D686M025AT]	68 uF [T494C686M004AT]
68 pF [CDR01BP680BKSM]	68 uF [T491B686M004AT]	68 uF [T491U686M004AT]	68 uF [T494C686M010AT]
68 uF [A700D686M008AT E015]	68 uF [T491B686M010AT]	68 uF [T491U686M006AT]	68 uF [T494C686M016AT]
68 uF [A700D686M008AT E018]	68 uF [T491C686M004AT]	68 uF [T491U686M010AT]	68 uF [T494D686M004AT]
68 uF [A700D686M010AT E015]	68 uF [T491C686M006AT]	68 uF [T491V686M010AT]	68 uF [T494D686M006AT]
68 uF [A700D686M010AT E018]	68 uF [T491C686M010AT]	68 uF [T491V686M016AT]	68 uF [T494D686M010AT]
	68 uF [T491C686M016AT]	68 uF [T491X686M020AT]	68 uF [T494D686M016AT]

Multisim 14.0 Full Components

68 uF [T494D686M020AT]	68 uF [T495D686M010AT E070]	68 uF [T495V686M010AT E140]	68 uF [T520B686M004AT E035]
68 uF [T494D686M025AT]	68 uF [T495D686M010AT E090]	68 uF [T495V686M016AT E300]	68 uF [T520B686M004AT E040]
68 uF [T494U686M004AT]	68 uF [T495D686M010AT E150]	68 uF [T495X686M010AT E150]	68 uF [T520B686M004AT E070]
68 uF [T494U686M006AT]	68 uF [T495D686M016AT E070]	68 uF [T495X686M020AT E150]	68 uF [T520B686M006AT E025]
68 uF [T494U686M010AT]	68 uF [T495D686M016AT E100]	68 uF [T495X686M025AT E125]	68 uF [T520B686M006AT E035]
68 uF [T494V686M010AT]	68 uF [T495D686M016AT E150]	68 uF [T495X686M025AT E200]	68 uF [T520B686M006AT E040]
68 uF [T494V686M016AT]	68 uF [T495D686M020AT E070]	68 uF [T513X686M025AH 6110]	68 uF [T520B686M006AT E070]
68 uF [T494X686M020AT]	68 uF [T495D686M020AT E150]	68 uF [T520A686M006AT E150]	68 uF [T520C686M006AT E100]
68 uF [T495B686M010AT E900]	68 uF [T495D686M025AT E150]	68 uF [T520A686M2R5AT E070]	68 uF [T520C686M010AT E045]
68 uF [T495C686M010AT E225]	68 uF [T495D686M025AT E200]	68 uF [T520A686M2R5AT E080]	68 uF [T520T686M004AT E070]
68 uF [T495D686M006AT E175]	68 uF [T495V686M010AT E100]	68 uF [T520B686M004AT E025]	68 uF [T520T686M006AT E070]

Multisim 14.0 Full Components

68 uF [T520T686M006AT E150]	68 uF [T521V686M016AT E050]	680 nF [C0805C684M4VAC TU]	680 nF [C1210C684M3VAC TU]
68 uF [T520U686M004AT E055]	68 uF [T521V686M016AT E090]	680 nF [C1206C684K3RACT U]	680 nF [C1210C684M5VAC TU]
68 uF [T520U686M006AT E055]	68 uF [T525B686M004AT E080]	680 nF [C1206C684K4RACT U]	680 nF [C1210F684K3RACT U]
68 uF [T520U686M006AT E070]	68 uF [T525B686M006AT E080]	680 nF [C1206C684K5RACT U]	680 nF [C1210F684K4RACT U]
68 uF [T520V686M010AT E025]	68 uF [T525T686M004AT E080]	680 nF [C1206C684K8RACT U]	680 nF [C1210F684K5RACT U]
68 uF [T520V686M010AT E040]	68 uF [T543U686M006AT E055]	680 nF [C1206C684M3VAC TU]	680 nF [C1812C684K5RACT U]
68 uF [T520V686M010AT E045]	680 nF [C0603C684K4PACT U]	680 nF [C1206C684M4VAC TU]	680 nF [C1812C684M5UAC TU]
68 uF [T520V686M010AT E060]	680 nF [C0603C684K8PACT U]	680 nF [C1206F684K4RACT U]	680 nF [C1812F684K1RACT U]
68 uF [T520V686M010AT E100]	680 nF [C0805C684K3PACT U]	680 nF [C1210C684K3RACT U]	680 nF [C1812F684K3RACT U]
68 uF [T520W686M010AT E040]	680 nF [C0805C684K4RACT U]	680 nF [C1210C684K4RACT U]	680 nF [C1812F684K5RACT U]
68 uF [T521D686M016AT E050]	680 nF [C0805C684K8RACT U]	680 nF [C1210C684K5RACT U]	680 nF [C1825C684K1RACT U]

Multisim 14.0 Full Components

680 nF [C1825C684K5RACT U]	680 nF [T491B684M050AT]	680 pF [C0402C681K4RACT U]	680 pF [C0603C681K5HACT U]
680 nF [C1825C684KARACT U]	680 nF [T491C684M050AT] 680 nF [T494A684M020AT]	680 pF [C0402C681K5HACT U]	680 pF [C0603C681K5RACT U]
680 nF [C2220C684K1RACT U]	680 nF [T494A684M025AT]	680 pF [C0402C681K5RACT U]	680 pF [C0805C681K1GACT U]
680 nF [C2220C684K5RACT U]	680 nF [T494A684M035AT]	680 pF [C0603C681K1HACT U]	680 pF [C0805C681K1RACT U]
680 nF [C2220C684KARACT U]	680 nF [T494B684M035AT]	680 pF [C0603C681K1RACT U]	680 pF [C0805C681K2RACT U]
680 nF [C2225C684K1RACT U]	680 nF [T494C684M050AT]	680 pF [C0603C681K2RACT U]	680 pF [C0805C681K4GACT U]
680 nF [C2225C684K5RACT U]	680 nF [T496C684M050AT 6110]	680 pF [C0603C681K3GACT U]	680 pF [C0805C681K4RACT U]
680 nF [C2225C684KARACT U]	680 pF [C0402C681K1HACT U]	680 pF [C0603C681K3HACT U]	680 pF [C0805C681K5GACT U]
680 nF [T491A684M020AT]	680 pF [C0402C681K3GACT U]	680 pF [C0603C681K3RACT U]	680 pF [C0805C681K5RACT U]
680 nF [T491A684M025AT]	680 pF [C0402C681K3HACT U]	680 pF [C0603C681K4RACT U]	680 pF [C1206C681K1GACT U]
680 nF [T491A684M035AT]	680 pF [C0402C681K3RACT U]	680 pF [C0603C681K5GACT U]	680 pF [C1206C681K2GACT U]
680 nF [T491B684M035AT]			

Multisim 14.0 Full Components

680 pF [C1206C681K5GACT U]	680 uF [T491E687M006AT]	680 uF [T513X687M006AH 6110]	680 uF [T520X687M004AT E015]
680 pF [C1206C681KCGAC TU]	680 uF [T491X687M004AT]	680 uF [T513X687M006AH 6120]	680 uF [T520X687M004AT E035]
680 pF [C1210C681KBGAC TU]	680 uF [T494D687M004AT]	680 uF [T520D687M003AT E015]	680 uF [T520Y687M004AT E010]
680 pF [C1210C681KCGAC TU]	680 uF [T494X687M004AT]	680 uF [T520D687M003AT E040]	680 uF [T520Y687M004AT E015]
680 pF [C1210C681KDGAC TU]	680 uF [T510E687M006AT E012]	680 uF [T520D687M004AT E012]	680 uF [T520Y687M004AT E025]
680 pF [C1812C681KBGAC TU]	680 uF [T510E687M006AT E023]	680 uF [T520D687M004AT E015]	680 uF [T520Y687M2R5AT E015]
680 pF [C1825C681KBGAC TU]	680 uF [T510X687M004AT E030]	680 uF [T520D687M004AT E025]	680 uF [T520Y687M2R5AT E025]
680 pF [C2220C681KBGAC TU]	680 uF [T510X687M006AT E023]	680 uF [T520D687M2R5AT E010]	680 uF [T525D687M003AT E025]
680 pF [C2220C681KZGACT U]	680 uF [T513E687M006AH 6110]	680 uF [T520D687M2R5AT E015]	680 uF [T525D687M2R5AT E025]
680 pF [C2225C681KBGAC TU]	680 uF [T513E687M006AH 6120]	680 uF [T520D687M2R5AT E040]	680 uF [T530D687M003AT E010]
680 uF [T491D687M004AT]	680 uF [T513X687M004AH 6110]	680 uF [T520X687M004AT E010]	680 uF [T530D687M2R5AT E006]

Multisim 14.0 Full Components

680 uF [T530D687M2R5AT E010]	6N1136	6N139-360E	73391-0060
	6N1136-X006	6POS_ROTARY	7400N
680 uF [T530X687M004AT E004]	6N1136-X009T	6SF5	7402N
	6N136	7.5 nF [C0603C752K3HACT U]	7403N
680 uF [T530X687M004AT E006]	6N136-000E		7404N
	6N136-020E	7.5 nF	7405N
680 uF [T530X687M004AT E010]	6N136-060E	[C0805C752K1GACT U]	7406N
	6N136-300E	7.5 nF	7407N
680 uF [T530X687M004AT E010]	6N136-320E	[C0805C752K1HACT U]	7408N
680 uF [T530X687M006AT E010]	6N136-360E	7.5 nF	7409N
	6N136-X001	[C0805C752K3HACT U]	74107N
680 uF [T530X687M006AT E018]	6N136-X006		74109N
	6N136-X007T	7.5 nF [C0805C752K5GACT U]	7410N
680 uF [T530Y687M004AT E005]	6N136-X009T		74116N
	6N136-X016	7.5 nF	74125N
680 uF [T530Y687M2R5AT E006]	6N136-X017T	[C0805C752K5HACT U]	74126N
	6N136-X019T	7.5 nF	7412N
680 uF [T543X687M004AT E015]	6N137	[C1206C752K1HACT U]	74132N
	6N137-X006	7.5 nF	74145N
690-009-521-900	6N137-X007T	[C1206C752K3HACT U]	74147N
	6N139-000E		74148N
6F6	6N139-020E	7.5 nF [C1206C752K5HACT U]	7414N
6J5	6N139-060E		74150N
6Line_Bussed	6N139-300E	7.5 nF	74151N
6Line_Isolated	6N139-320E	[CDR34BP752AKSM]	74153N

Multisim 14.0 Full Components

74154N	741-DIV	74393N	74HC00N_4V
74155N	7420N	7439N	74HC00N_6V
74156N	7422N	7440N	74HC02D_2V
74157N	74251J	7442N	74HC02D_4V
74159N	74251N	7445N	74HC02D_6V
74160N	7425N	7446N	74HC02N_2V
74162N	7426N	7447N	74HC02N_4V
74163N	74279N	7451N	74HC02N_6V
74164N	7427N	7454N	74HC03D_2V
74165N	7428N	7472N	74HC03D_4V
74166N	74290N	7473N	74HC03D_6V
7416N	74293N	7474N	74HC03N_2V
74173N	74298N	7475N	74HC03N_4V
74174N	7430N	7476N	74HC03N_6V
74175N	74320-1004	7477W	74HC04D_2V
7417N	74320-3004	7486N	74HC04D_4V
74181J	74320-4004	749070-9	74HC04D_6V
74181N	74320-5000	7490N	74HC04N_2V
74190N	7432N	7491N	74HC04N_4V
74191N	7433N	7492N	74HC04N_6V
74192N	74365N	7493N	74HC05D_2V
74194N	74367N	74HC00D_2V	74HC05D_4V
74195N	74368N	74HC00D_4V	74HC05D_6V
74198N	7437N	74HC00D_6V	74HC05N_2V
74199N	7438N	74HC00N_2V	74HC05N_4V

Multisim 14.0 Full Components

74HC05N_6V	74HC10D_2V	74HC11D_4V	74HC138D_4V
74HC08D_2V	74HC10D_4V	74HC11D_6V	74HC138D_4V
74HC08D_4V	74HC10D_6V	74HC11N_2V	74HC138D_6V
74HC08D_6V	74HC10N_2V	74HC11N_4V	74HC138N_2V
74HC08N_2V	74HC10N_4V	74HC11N_6V	74HC138N_4V
74HC08N_4V	74HC10N_6V	74HC125N_2V	74HC138N_4V
74HC08N_6V	74HC112D_2V	74HC125N_4V	74HC138N_6V
74HC09D_2V	74HC112D_4V	74HC125N_6V	74HC139DW_2V
74HC09D_4V	74HC112D_6V	74HC126N_2V	74HC139DW_4V
74HC09D_6V	74HC112N_2V	74HC126N_4V	74HC139DW_6V
74HC09N_2V	74HC112N_4V	74HC126N_6V	74HC139N_2V
74HC09N_4V	74HC112N_6V	74HC133D_2V	74HC139N_4V
74HC09N_6V	74HC113D_2V	74HC133D_4V	74HC139N_6V
74HC107D_2V	74HC113D_4V	74HC133D_4V	74HC147N_2V
74HC107D_4V	74HC113D_6V	74HC133D_6V	74HC147N_4V
74HC107D_6V	74HC113N_2V	74HC133N_2V	74HC147N_6V
74HC107N_2V	74HC113N_4V	74HC133N_4V	74HC148DW_2V
74HC107N_4V	74HC113N_6V	74HC133N_6V	74HC148DW_4V
74HC107N_6V	74HC114D_2V	74HC137D_2V	74HC148DW_6V
74HC109D_2V	74HC114D_4V	74HC137D_4V	74HC148N_2V
74HC109D_4V	74HC114D_6V	74HC137D_6V	74HC148N_4V
74HC109D_6V	74HC114N_2V	74HC137N_2V	74HC148N_6V
74HC109N_2V	74HC114N_4V	74HC137N_4V	74HC151D_2V
74HC109N_4V	74HC114N_6V	74HC137N_6V	74HC151D_4V
74HC109N_6V	74HC11D_2V	74HC138D_2V	74HC151D_6V

Multisim 14.0 Full Components

74HC151N_2V	74HC157D_4V	74HC163D_6V	74HC174D_2V
74HC151N_4V	74HC157D_6V	74HC163N_2V	74HC174D_4V
74HC151N_6V	74HC157N_2V	74HC163N_4V	74HC174D_6V
74HC152D_2V	74HC157N_4V	74HC163N_6V	74HC174N_2V
74HC152D_4V	74HC157N_6V	74HC164N_2V	74HC174N_4V
74HC152D_6V	74HC158D_2V	74HC164N_4V	74HC174N_6V
74HC152N_2V	74HC158D_4V	74HC164N_6V	74HC175D_2V
74HC152N_4V	74HC158D_6V	74HC165D_2V	74HC175D_4V
74HC152N_6V	74HC158N_2V	74HC165D_4V	74HC175D_6V
74HC153D_2V	74HC158N_4V	74HC165D_6V	74HC175N_2V
74HC153D_4V	74HC158N_6V	74HC165N_2V	74HC175N_4V
74HC153D_6V	74HC160D_2V	74HC165N_4V	74HC175N_6V
74HC153DW_2V	74HC160D_4V	74HC165N_6V	74HC190D_2V
74HC153DW_4V	74HC160D_6V	74HC166D_2V	74HC190D_4V
74HC153DW_6V	74HC160N_2V	74HC166D_4V	74HC190D_6V
74HC153N_2V	74HC160N_4V	74HC166D_6V	74HC190N_2V
74HC153N_4V	74HC160N_6V	74HC166N_2V	74HC190N_4V
74HC153N_6V	74HC162D_2V	74HC166N_4V	74HC190N_6V
74HC154DW_2V	74HC162D_4V	74HC166N_6V	74HC191D_2V
74HC154DW_4V	74HC162D_6V	74HC173D_2V	74HC191D_4V
74HC154DW_6V	74HC162N_2V	74HC173D_4V	74HC191D_6V
74HC154NT_2V	74HC162N_4V	74HC173D_6V	74HC191N_2V
74HC154NT_4V	74HC162N_6V	74HC173N_2V	74HC191N_4V
74HC154NT_6V	74HC163D_2V	74HC173N_4V	74HC191N_6V
74HC157D_2V	74HC163D_4V	74HC173N_6V	74HC192D_2V

Multisim 14.0 Full Components

74HC192D_4V	74HC240DW_6V	74HC253D_6V	74HC273N_2V
74HC192D_6V	74HC240N_2V	74HC253N_2V	74HC273N_4V
74HC192N_2V	74HC240N_4V	74HC253N_4V	74HC273N_6V
74HC192N_4V	74HC240N_6V	74HC253N_6V	74HC27D_2V
74HC192N_6V	74HC241DW_2V	74HC257D_2V	74HC27D_4V
74HC194N_2V	74HC241DW_4V	74HC257D_4V	74HC27D_6V
74HC194N_4V	74HC241DW_6V	74HC257D_6V	74HC27N_2V
74HC194N_6V	74HC241N_2V	74HC257N_2V	74HC27N_4V
74HC195N_2V	74HC241N_4V	74HC257N_4V	74HC27N_6V
74HC195N_4V	74HC241N_6V	74HC257N_6V	74HC280D_2V
74HC195N_6V	74HC244_4V	74HC258D_2V	74HC280D_4V
74HC20D_2V	74HC244DW_2V	74HC258D_4V	74HC280D_6V
74HC20D_4V	74HC244DW_4V	74HC258D_6V	74HC280N_2V
74HC20D_6V	74HC244DW_6V	74HC258N_2V	74HC280N_4V
74HC20N_2V	74HC244N_2V	74HC258N_4V	74HC280N_6V
74HC20N_4V	74HC244N_4V	74HC258N_6V	74HC283D_2V
74HC20N_6V	74HC244N_6V	74HC266D_2V	74HC283D_4V
74HC21D_2V	74HC251D_2V	74HC266D_4V	74HC283D_6V
74HC21D_4V	74HC251D_4V	74HC266D_6V	74HC283N_2V
74HC21D_6V	74HC251D_6V	74HC266N_2V	74HC283N_4V
74HC21N_2V	74HC251N_2V	74HC266N_4V	74HC283N_6V
74HC21N_4V	74HC251N_4V	74HC266N_6V	74HC298N_2V
74HC21N_6V	74HC251N_6V	74HC273DW_2V	74HC298N_4V
74HC240DW_2V	74HC253D_2V	74HC273DW_4V	74HC298N_6V
74HC240DW_4V	74HC253D_4V	74HC273DW_6V	74HC30D_2V

Multisim 14.0 Full Components

74HC30D_4V	74HC367N_4V	74HC375N_6V	74HC42D_2V
74HC30D_6V	74HC367N_6V	74HC377DW_2V	74HC42D_4V
74HC30N_2V	74HC368D_2V	74HC377DW_4V	74HC42D_6V
74HC30N_4V	74HC368D_4V	74HC377DW_6V	74HC42N_2V
74HC30N_6V	74HC368D_6V	74HC377N_2V	74HC42N_4V
74HC32D_2V	74HC368N_2V	74HC377N_4V	74HC42N_6V
74HC32D_4V	74HC368N_4V	74HC377N_6V	74HC51D_2V
74HC32D_6V	74HC368N_6V	74HC378D_2V	74HC51D_4V
74HC32N_2V	74HC373DW_2V	74HC378D_4V	74HC51D_6V
74HC32N_4V	74HC373DW_4V	74HC378D_6V	74HC51N_2V
74HC32N_6V	74HC373DW_6V	74HC378N_2V	74HC51N_4V
74HC365D_2V	74HC373N_2V	74HC378N_4V	74HC51N_6V
74HC365D_4V	74HC373N_4V	74HC378N_6V	74HC73D_2V
74HC365D_6V	74HC373N_6V	74HC379D_2V	74HC73D_4V
74HC365N_2V	74HC374DW_2V	74HC379D_4V	74HC73D_6V
74HC365N_4V	74HC374DW_4V	74HC379D_6V	74HC73N_2V
74HC365N_6V	74HC374DW_6V	74HC379J_2V	74HC73N_4V
74HC366D_2V	74HC374N_2V	74HC379J_4V	74HC73N_6V
74HC366D_6V	74HC374N_4V	74HC379J_6V	74HC74D_2V
74HC366N_2V	74HC374N_6V	74HC379N_2V	74HC74D_4V
74HC366N_6V	74HC375D_2V	74HC379N_4V	74HC74D_6V
74HC367D_2V	74HC375D_4V	74HC379N_6V	74HC74N_2V
74HC367D_4V	74HC375D_6V	74HC393N_2V	74HC74N_4V
74HC367D_6V	74HC375N_2V	74HC393N_4V	74HC74N_6V
74HC367N_2V	74HC375N_4V	74HC393N_6V	74HC75D_2V

Multisim 14.0 Full Components

74HC75D_4V	74HC86D_6V	74LS08D	74LS113D
74HC75D_6V	74HC86N_2V	74LS08J	74LS113D
74HC75N_2V	74HC86N_4V	74LS08J	74LS113N
74HC75N_4V	74HC86N_6V	74LS08N	74LS113N
74HC75N_6V	74LS00D	74LS08N	74LS114D
74HC76D_2V	74LS00D	74LS09D	74LS114D
74HC76D_4V	74LS00N	74LS09D	74LS114N
74HC76D_6V	74LS00N	74LS09N	74LS114N
74HC76N_2V	74LS02D	74LS09N	74LS11D
74HC76N_4V	74LS02D	74LS107D	74LS11D
74HC76N_6V	74LS02N	74LS107D	74LS11N
74HC77D_2V	74LS02N	74LS107N	74LS11N
74HC77D_4V	74LS03D	74LS107N	74LS125D
74HC77D_6V	74LS03D	74LS109D	74LS125D
74HC77N_2V	74LS03N	74LS109D	74LS125N
74HC77N_4V	74LS03N	74LS109N	74LS126D
74HC77N_6V	74LS04D	74LS109N	74LS126D
74HC78D_2V	74LS04D	74LS10D	74LS126N
74HC78D_4V	74LS04N	74LS10D	74LS12D
74HC78D_6V	74LS04N	74LS10N	74LS12D
74HC78N_2V	74LS05D	74LS10N	74LS12N
74HC78N_4V	74LS05D	74LS112D	74LS12N
74HC78N_6V	74LS05N	74LS112D	74LS132D
74HC86D_2V	74LS05N	74LS112N	74LS132N
74HC86D_4V	74LS08D	74LS112N	74LS138D

Multisim 14.0 Full Components

74LS138D	74LS153D	74LS160D	74LS169N
74LS138N	74LS153D	74LS160N	74LS169N
74LS138N	74LS153N	74LS160N	74LS173D
74LS139D	74LS153N	74LS162D	74LS173D
74LS139D	74LS155D	74LS162D	74LS173N
74LS139N	74LS155D	74LS162N	74LS173N
74LS139N	74LS155N	74LS162N	74LS174D
74LS145D	74LS155N	74LS163D	74LS174D
74LS145D	74LS156D	74LS163D	74LS174N
74LS145N	74LS156D	74LS163N	74LS174N
74LS145N	74LS156N	74LS163N	74LS175D
74LS147D	74LS156N	74LS164D	74LS175D
74LS147D	74LS157D	74LS164D	74LS175N
74LS147N	74LS157D	74LS164N	74LS175N
74LS147N	74LS157N	74LS164N	74LS181DW
74LS148D	74LS157N	74LS165D	74LS181DW
74LS148D	74LS158D	74LS165D	74LS181N
74LS148N	74LS158D	74LS165N	74LS181N
74LS148N	74LS158N	74LS165N	74LS190D
74LS14D	74LS158N	74LS166D	74LS190D
74LS14N	74LS15D	74LS166D	74LS190N
74LS151D	74LS15D	74LS166N	74LS190N
74LS151D	74LS15N	74LS166N	74LS191D
74LS151N	74LS15N	74LS169D	74LS191D
74LS151N	74LS160D	74LS169D	74LS191N

Multisim 14.0 Full Components

74LS191N	74LS240DW	74LS258N	74LS28N
74LS192D	74LS240DW	74LS266D	74LS28N
74LS192D	74LS240N	74LS266D	74LS290D
74LS192N	74LS240N	74LS266N	74LS290D
74LS192N	74LS241DW	74LS266N	74LS290N
74LS194D	74LS241DW	74LS26D	74LS290N
74LS194D	74LS241N	74LS26D	74LS293D
74LS194N	74LS241N	74LS26N	74LS293D
74LS194N	74LS244DW	74LS26N	74LS293N
74LS195D	74LS244N	74LS273DW	74LS293N
74LS195D	74LS251D	74LS273DW	74LS298D
74LS195N	74LS251D	74LS273N	74LS298D
74LS195N	74LS251N	74LS273N	74LS298N
74LS20D	74LS251N	74LS279D	74LS298N
74LS20D	74LS253D	74LS279N	74LS30D
74LS20N	74LS253D	74LS27D	74LS30N
74LS20N	74LS253N	74LS27D	74LS30N
74LS21D	74LS253N	74LS27N	74LS32D
74LS21D	74LS257D	74LS27N	74LS32D
74LS21N	74LS257D	74LS280D	74LS32N
74LS21N	74LS257N	74LS280D	74LS32N
74LS22D	74LS257N	74LS280N	74LS33D
74LS22D	74LS258D	74LS280N	74LS33D
74LS22N	74LS258D	74LS28D	74LS33N
74LS22N	74LS258N	74LS28D	74LS33N

Multisim 14.0 Full Components

74LS348D	74LS374DW	74LS393D	74LS465N
74LS348N	74LS374DW	74LS393D	74LS466DW
74LS352D	74LS374N	74LS393N	74LS466DW
74LS352D	74LS374N	74LS393N	74LS466N
74LS352N	74LS375D	74LS395D	74LS466N
74LS352N	74LS375N	74LS395D	74LS47D
74LS353D	74LS377DW	74LS395N	74LS47D
74LS353D	74LS377DW	74LS395N	74LS47N
74LS353N	74LS377N	74LS399D	74LS47N
74LS365D	74LS377N	74LS399N	74LS48D
74LS365D	74LS378D	74LS40D	74LS48N
74LS365N	74LS378D	74LS40D	74LS51D
74LS365N	74LS378N	74LS40N	74LS51D
74LS367D	74LS378N	74LS40N	74LS51N
74LS367D	74LS379D	74LS42D	74LS51N
74LS367N	74LS379D	74LS42D	74LS540DW
74LS367N	74LS379N	74LS42N	74LS540N
74LS368D	74LS379N	74LS42N	74LS541DW
74LS368D	74LS37D	74LS445D	74LS541N
74LS368N	74LS37D	74LS445D	74LS54D
74LS368N	74LS37N	74LS445N	74LS54D
74LS373DW	74LS38D	74LS445N	74LS54N
74LS373DW	74LS38D	74LS465DW	74LS54N
74LS373N	74LS38N	74LS465DW	74LS55D
74LS373N	74LS38N	74LS465N	74LS55D

Multisim 14.0 Full Components

74LS55N	74LS78D	74STD116N	75 pF [C1206C750KBGAC TU]
74LS55N	74LS78N	74STD150N	
74LS69D	74LS78N	74STD154N	75 pF [C1210C750KBGAC TU]
74LS69D	74LS86D	74STD159N	
74LS69N	74LS86D	74STD16N	75 pF [C1812C750KBGAC TU]
74LS69N	74LS86N	74STD17N	
74LS73D	74LS86N	74STD198N	
74LS73D	74LS90D	74STD199N	75 pF [C1825C750KBGAC TU]
74LS73N	74LS90D	74STD25N	
74LS73N	74LS90N	74STD39N	75 pF [C2220C750KBGAC TU]
74LS74D	74LS90N	74STD45N	
74LS74D	74LS91D	74STD72N	75 pF [C2225C750KBGAC TU]
74LS74N	74LS91D	75 mF [C0805C759KBGAC TU]	
74LS74N	74LS91N		750 pF [C0402C751K1HACT U]
74LS75D	74LS91N	75 pF [C0603C750K5GACT U]	
74LS75D	74LS92D		750 pF [C0402C751K3HACT U]
74LS75N	74LS92D	75 pF [C0805C750K2GACT U]	
74LS75N	74LS92N		750 pF [C0402C751K5HACT U]
74LS76D	74LS92N		
74LS76D	74LS93D	75 pF [C0805C750KBGAC TU]	
74LS76N	74LS93D		750 pF [C0603C751K1HACT U]
74LS76N	74LS93N	75 pF [C0805C750KCGAC TU]	
74LS77W	74LS93N		750 pF [C0603C751K3HACT U]
74LS77W	74STD06N	75 pF [C1206C750K5GACT U]	
74LS78D	74STD07N		

Multisim 14.0 Full Components

750 pF [C0603C751K5GACT U]	8.2 nF [C0402C822K4RACT U]	8.2 nF [C0805C822K1RACT U]	8.2 nF [C1206C822K2RACT U]
750 pF [C0603C751K5HACT U]	8.2 nF [C0402C822K5RACT U]	8.2 nF [C0805C822K2RACT U]	8.2 nF [C1206C822K3HACT U]
750 pF [C1210C751KBGAC TU]	8.2 nF [C0402C822K9RACT U]	8.2 nF [C0805C822K3GACT U]	8.2 nF [C1206C822K5HACT U]
750 pF [C1812C751KBGAC TU]	8.2 nF [C0603C822K1RACT U]	8.2 nF [C0805C822K3HACT U]	8.2 nF [C1206C822K5RACT U]
750 pF [C1825C751KBGAC TU]	8.2 nF [C0603C822K3GACT U]	8.2 nF [C0805C822K3RACT U]	8.2 nF [C1206C822KARACT U]
750 pF [C2220C751KBGAC TU]	8.2 nF [C0603C822K3HACT U]	8.2 nF [C0805C822K4RACT U]	8.2 nF [C1210C822K5GACT U]
750 pF [C2225C751KBGAC TU]	8.2 nF [C0603C822K3RACT U]	8.2 nF [C0805C822K5GACT U]	8.2 nF [C1210C822K5RACT U]
777778-01	8.2 nF [C0603C822K4RACT U]	8.2 nF [C0805C822K5HACT U]	8.2 nF [C1210C822KARACT U]
777779-01			
779157-01	8.2 nF [C0603C822K5RACT U]	8.2 nF [C0805C822K5RACT U]	8.2 nF [C1812C822K5GACT U]
781334-01			
7Line_Bussed	8.2 nF	8.2 nF	8.2 nF
7Line_Isolated	[C0805C822K1GACT U]	[C1206C822K1HACT U]	[C1812C822K5RACT U]
7POS_ROTARY			
8.2 nF [C0402C822K3RACT U]	8.2 nF [C0805C822K1HACT U]	8.2 nF [C1206C822K1RACT U]	8.2 nF [C2220C822K2GACT U]

Multisim 14.0 Full Components

8.2 uF [A700V825M016AT E045]	80C188EB13 80C188EB20	82 nF [C0603C823K3RACT U]	82 nF [C0805F823K4RACT U]
8.2 uF [C1206C825K4PACT U]	80C188EB25 80L186EA13	82 nF [C0603C823K4RACT U]	82 nF [C0805F823K5RACT U]
8.2 uF [C1206C825K8PACT U]	80L186EB13 80L186EB16	82 nF [C0603C823K5RACT U]	82 nF [C1206C823K1RACT U]
8.2 uF [C1206C825K8RACT U]	80L188EA13 80L188EB13	82 nF [C0603C823K8RACT U]	82 nF [C1206C823K2RACT U]
8.2 uF [C1206C825K9RACT U]	80L188EB16 80SQ045NG	82 nF [C0805C823K1RACT U]	82 nF [C1206C823K3HACT U]
8.2 uF [C1206C825K9RACT U]	80SQ045NRLG		
8.2 uF [C1210C825K3PACT U]	82 mF [C0603C829K2GACT U]	82 nF [C0805C823K3RACT U]	82 nF [C1206C823K3RACT U]
8.2 uF [C1210C825K4PACT U]	82 mF [C0805C829K5GACT U]	82 nF [C0805C823K4RACT U]	82 nF [C1206C823K5HACT U]
80C186EA13	82 mF [C0805C829KBGAC TU]	82 nF [C0805C823K5RACT U]	82 nF [C1206C823K5RACT U]
80C186EA20			
80C186EA25	82 nF [C0402C823K4RACT U]	82 nF [C0805C823K8RACT U]	82 nF [C1206C823KARACT U]
80C186EB13			
80C186EB20	82 nF [C0402C823K8RACT U]	82 nF [C0805C823M5UAC TU]	82 nF [C1206C823M5UAC TU]
80C186EB25			
80C188EA13	82 nF [C0402C823K9RACT U]	82 nF [C0805F823K3RACT U]	82 nF [C1206F823K1RACT U]
80C188EA20			
80C188EA25			

Multisim 14.0 Full Components

82 nF [C1206F823K3RACT U]	82 nF [C1210C823M1UAC TU]	82 pF [C0402C820K3GACT U]	82 pF [C1206C820KBGAC TU]
82 nF [C1206F823K4RACT U]	82 nF [C1210F823K2RACT U]	82 pF [C0402C820K5GACT U]	82 pF [C1206C820KCGAC TU]
82 nF [C1206F823K5RACT U]	82 nF [C1812C823K1GACT U]	82 pF [C0603C820K5GACT U]	82 pF [C1210C820KBGAC TU]
82 nF [C1210C823K1GACT U]	82 nF [C1812C823K1HACT U]	82 pF [C0805C820K1GACT U]	82 pF [C1812C820KBGAC TU]
82 nF [C1210C823K1HACT U]	82 nF [C1812C823K5GACT U]	82 pF [C0805C820K2GACT U]	82 pF [C1825C820KBGAC TU]
82 nF [C1210C823K1RACT U]	82 nF [C1812C823K5HACT U]	82 pF [C0805C820K3GACT U]	82 pF [C2220C820KBGAC TU]
82 nF [C1210C823K3HACT U]	82 nF [C1812C823K5RACT U]	82 pF [C0805C820K5GACT U]	82 pF [C2225C820KBGAC TU]
82 nF [C1210C823K5GACT U]	82 nF [C2220C823K1GACT U]	82 pF [C0805C820KBGAC TU]	82 pF [CA064C820K2GAC TU]
82 nF [C1210C823K5HACT U]	82 nF [C2220C823K2GACT U]	82 pF [C1206C820K1GACT U]	82 pF [CDR31BP820BKSM]
82 nF [C1210C823K5RACT U]	82 nF [C2220C823K5GACT U]	82 pF [C1206C820K2GACT U]	82 uF [A700V826M004AT E018]
82 nF [C1210C823KARACT U]	82 pF [C0201C820K3GACT U]	82 pF [C1206C820K5GACT U]	82 uF [A700V826M004AT E025]

Multisim 14.0 Full Components

82 uF [A700V826M004AT E028]	820 nF [C0805C824K8RACT U]	820 nF [C1812F824K3RACT U]	820 pF [C0402C821K3RACT U]
82 uF [A700V826M006AT E018]	820 nF [C1206C824K3RACT U]	820 nF [C1812F824K5RACT U]	820 pF [C0402C821K4RACT U]
82 uF [A700V826M006AT E025]	820 nF [C1206C824K4RACT U]	820 nF [C1825C824KARACT U]	820 pF [C0402C821K5HACT U]
82 uF [A700V826M006AT E028]	820 nF [C1206F824K4RACT U]	820 nF [C2220C824K1RACT U]	820 pF [C0402C821K5RACT U]
82 uF [A700V826M2R5AT E018]	820 nF [C1210C824K5RACT U]	820 nF [C2220C824K5RACT U]	820 pF [C0402C821K8RACT U]
82 uF [A700V826M2R5AT E025]	820 nF [C1210C824K8RACT U]	820 nF [C2220C824KARACT U]	820 pF [C0603C821K1HACT U]
82 uF [A700V826M2R5AT E028]	820 nF [C1210F824K3RACT U]	820 nF [C2225C824K5RACT U]	820 pF [C0603C821K1RACT U]
82 uF [T520C826M008AT E025]	820 nF [C1210F824K4RACT U]	820 nF [C2225C824KARACT U]	820 pF [C0603C821K2RACT U]
82 uF [T520C826M008AT E045]	820 nF [C1812C824K5RACT U]	820 pF [C0402C821K1HACT U]	820 pF [C0603C821K3GACT U]
820 nF [C0603C824K8PACT U]	820 nF [C1812C824M5UAC TU]	820 pF [C0402C821K3GACT U]	820 pF [C0603C821K3HACT U]
820 nF [C0805C824K4RACT U]	820 nF [C1812F824K1RACT U]	820 pF [C0402C821K3HACT U]	820 pF [C0603C821K3RACT U]

Multisim 14.0 Full Components

820 pF [C0603C821K4RACT U]	820 pF [C1206C821K2GACT U]	8Line_Isolated 8POS_ROTARY	9.1 nF [CDR35BP912BKSM]
820 pF [C0603C821K5GACT U]	820 pF [C1206C821K5GACT U]	9.1 nF [C0603C912K3HACT U]	91 mF [C0805C919KBGAC TU]
820 pF [C0603C821K5HACT U]	820 pF [C1210C821KBGAC TU]	9.1 nF [C0805C912K1GACT U]	91 pF [C0805C910K2GACT U]
820 pF [C0603C821K5RACT U]	820 pF [C1812C821K2GACT U]	9.1 nF [C0805C912K1HACT U]	91 pF [C0805C910KBGAC TU]
820 pF [C0805C821K1RACT U]	820 pF [C1812C821K5GACT U]	9.1 nF [C0805C912K3HACT U]	91 pF [C1206C910K1GACT U]
820 pF [C0805C821K2RACT U]	820 pF [C1812C821KBGAC TU]	9.1 nF [C0805C912K5GACT U]	91 pF [C1206C910KBGAC TU]
820 pF [C0805C821K4GACT U]	820 pF [C1825C821KBGAC TU]	9.1 nF [C0805C912K5HACT U]	91 pF [C1210C910KBGAC TU]
820 pF [C0805C821K4RACT U]	820 pF [C2220C821KBGAC TU]	9.1 nF [C1206C912K1HACT U]	91 pF [C1812C910KBGAC TU]
820 pF [C0805C821K5GACT U]	820 pF [C2225C821KBGAC TU]	9.1 nF [C1206C912K3GACT U]	91 pF [C1825C910KBGAC TU]
820 pF [C0805C821K5RACT U]	820 pF [CDR32BP821BKSM]	9.1 nF [C1206C912K3HACT U]	91 pF [C2220C910KBGAC TU]
820 pF [C1206C821K1GACT U]	8550-4500PL 87520-0010BLF 8Line_Bussed	9.1 nF [C1206C912K5HACT U]	91 pF [C2225C910KBGAC TU]

Multisim 14.0 Full Components

910 pF [C0402C911K1HACT U]	910 pF [C2220C911KBGAC TU]	ACB1608L-015	ACB2012M-600
		ACB1608L-030	ACC2012L-250
910 pF [C0402C911K3HACT U]	910 pF [C2225C911KBGAC TU]	ACB1608L-060	ACC3216L-500
		ACB1608L-120	ACC4516L-700
910 pF [C0402C911K5HACT U]	9Line_Bussed	ACB1608L-300	ACML-7400-000E
	9Line_Isolated	ACB1608M-040	ACML-7410-000E
910 pF [C0603C911K1HACT U]	ABM_CURRENT	ACB1608M-080	ACML-7420-000E
	ABM_VOLTAGE	ACB1608M-120	ACNW261L-000E
910 pF [C0603C911K3HACT U]	AC_CURRENT	ACB1608M-300	ACNW261L-300E
	AC_POWER	ACB1608M-600	ACPL-021L-000E
910 pF [C0603C911K5HACT U]	AC_VOLTAGE	ACB2012H-015	ACPL-021L-060E
		ACB2012H-030	ACPL-024L-000E
910 pF [C0603C911K5GACT U]	ACA3216H4-060	ACB2012H-060	ACPL-024L-060E
	ACA3216H4-120	ACB2012H-120	ACPL-054L-000E
910 pF [C0603C911K5HACT U]	ACA3216H4-300	ACB2012H-300	ACPL-054L-060E
	ACA3216M3-600	ACB2012L-015	ACPL-061L-000E
910 pF [C0805C911K5GACT U]	ACA3216M4-060	ACB2012L-030	ACPL-061L-060E
	ACA3216M4-120	ACB2012L-060	ACPL-064L-000E
910 pF [C1210C911KBGAC TU]	ACA3216M4-300	ACB2012L-120	ACPL-064L-060E
	ACA3216M4-600	ACB2012L-300	ACPL-077L-000E
910 pF [C1812C911KBGAC TU]	ACB1608H-015	ACB2012L-600	ACPL-077L-060E
	ACB1608H-030	ACB2012M-040	ACPL-0820-000E
910 pF [C1825C911KBGAC TU]	ACB1608H-060	ACB2012M-080	ACPL-214-500E
	ACB1608H-120	ACB2012M-120	ACPL-214-50AE
	ACB1608H-300	ACB2012M-300	ACPL-214-560E

Multisim 14.0 Full Components

ACPL-214-56AE	ACPL-C79A-000E	ACPL-M50L-000E	ACPL-W343-060E
ACPL-217-500E	ACPL-C79B-000E	ACPL-M50L-060E	ACPL-W345-000E
ACPL-217-50AE	ACPL-C87AT-000E	ACPL-M61L-000E	ACPL-W345-060E
ACPL-217-50BE	ACPL-H342-000E	ACPL-M61L-060E	ACPL-W346-000E
ACPL-217-50CE	ACPL-H342-060E	ACPL-M61T-000E	ACPL-W346-060E
ACPL-217-50DE	ACPL-K342-000E	ACPL-M61T-060E	ACPL-W50L-000E
ACPL-217-560E	ACPL-K342-060E	ACPL-M71T-000E	ACPL-W50L-060E
ACPL-217-56AE	ACPL-K34T-000E	ACPL-M71T-060E	ACPL-W61L-000E
ACPL-217-56BE	ACPL-K34T-060E	ACPL-M72T-000E	ACPL-W61L-060E
ACPL-217-56CE	ACPL-K43T-000E	ACPL-M72T-060E	ACSL-6400-00TE
ACPL-217-56DE	ACPL-K43T-060E	ACPL-P340-000E	ACSL-6400-06TE
ACPL-312U-000E	ACPL-K44T-000E	ACPL-P340-060E	ACSL-7210-00RE
ACPL-312U-300E	ACPL-K44T-060E	ACPL-P341-000E	ACSL-7210-06RE
ACPL-32JT-000E	ACPL-K54L-000E	ACPL-P341-060E	ACTEL-FLASHPRO-HDR
ACPL-331J-000E	ACPL-K54L-060E	ACPL-P343-000E	AD1580ART
ACPL-332J-000E	ACPL-K64L-000E	ACPL-P343-060E	AD1580ARTZ
ACPL-336J-000E	ACPL-K64L-060E	ACPL-P345-000E	AD1580BKSZ
ACPL-337J-000E	ACPL-M21L-000E	ACPL-P345-060E	AD1580BRT
ACPL-339J-000E	ACPL-M21L-060E	ACPL-P346-000E	AD1580BRTZ
ACPL-34JT-000E	ACPL-M43T-000E	ACPL-P346-060E	AD22050N
ACPL-782T-000E	ACPL-M43T-060E	ACPL-W340-000E	AD22050R
ACPL-782T-300E	ACPL-M46T-000E	ACPL-W340-060E	AD22057N
ACPL-C61L-000E	ACPL-M46T-060E	ACPL-W341-000E	AD22057R
ACPL-C61L-060E	ACPL-M49T-000E	ACPL-W341-060E	AD380JH
ACPL-C790-000E	ACPL-M49T-060E	ACPL-W343-000E	

Multisim 14.0 Full Components

AD380KH	AD542KH	AD548JN	AD584JN
AD380LH	AD542LH	AD548JR	AD584KH
AD380SH	AD542SH	AD548KN	AD584KN
AD507JH	AD544JH	AD548SH	AD584LH
AD507KH	AD544KH	AD548SQ	AD584SH
AD507SH	AD544LH	AD548TH	AD584TH
AD509JH	AD544SH	AD548TQ	AD587JN
AD509KH	AD545AJH	AD549JH	AD587JNZ
AD509SH	AD545AKH	AD549KH	AD587JQ
AD515AJH	AD545ALH	AD549LH	AD587JR
AD515AKH	AD545AMH	AD549SH	AD587JRZ
AD515ALH	AD546JN	AD549SH/883B	AD587KN
AD517JH	AD546KN	AD5530_SO16	AD587KR
AD517KH	AD547JH	AD5531_SO16	AD587KRZ
AD517LH	AD547KH	AD5539JN	AD587UQ
AD517SH	AD547LH	AD5539JQ	AD588AD
AD5260_SO14	AD547SH	AD5539SQ	AD588AQ
AD5262_SO16	AD548AH	AD5539SQ/883B	AD588ARWZ
AD5280_SO14	AD548AQ	AD581JH	AD588BD
AD5282_SO16	AD548AR	AD581KH	AD588BQ
AD536AJD	AD548BH	AD581LH	AD588JQ
AD536AJH	AD548BQ	AD581SH	AD588KQ
AD536AJQ	AD548BR	AD581TH	AD588SD
AD536ASE/883B	AD548CH	AD581UH	AD588TD
AD542JH	AD548CQ	AD584JH	AD588TQ/883B

Multisim 14.0 Full Components

AD600AQ	AD624CD	AD633JR	AD642SH
AD600AR	AD624SD	AD636JD	AD644JH
AD600JN	AD626AN	AD636JH	AD644KH
AD602AQ	AD626AR	AD636KD	AD644LH
AD602AR	AD626BN	AD636KH	AD644SH
AD602JN	AD627AN	AD637AQ	AD645AH
AD603AQ	AD627AR	AD637AR	AD645BH
AD603AR	AD627BN	AD637ARZ	AD645JN
AD604AN	AD627BR	AD637BR	AD645KN
AD604AR	AD628ARMZ	AD637BRZ	AD645SH
AD604ARS	AD628ARZ	AD637JD	AD647JH
AD605AN	AD629AN	AD637JDZ	AD647KH
AD605AR	AD629AR	AD637JQ	AD647LH
AD620AN	AD629BN	AD637JRZ	AD647SE
AD620AR	AD629BR	AD637JRZ-R7	AD647SEB
AD620BN	AD630AD	AD637JRZ-RL	AD647SH
AD620BR	AD630AR	AD637KDZ	AD680AN
AD620SQ	AD630BD	AD637KQ	AD680AR
AD623AN	AD630JN	AD637KRZ	AD680JR
AD623AR	AD630KN	AD637SD	AD680JTZ
AD623ARM	AD630SD	AD637SD/883B	AD704AN
AD623BN	AD630SE/883B	AD637SQ/883B	AD704AQ
AD623BR	AD633AN	AD642JH	AD704AR
AD624AD	AD633AR	AD642KH	AD704BQ
AD624BD	AD633JN	AD642LH	AD704JN

Multisim 14.0 Full Components

AD704JR	AD707TQ	AD712BH	AD734AQ
AD704JR-16	AD708AH	AD712BQ	AD734BN
AD704KN	AD708AQ	AD712CH	AD734BQ
AD704TQ	AD708BH	AD712CQ	AD734SQ
AD704TQ/883B	AD708BQ	AD712JN	AD734SQ/883B
AD705AQ	AD708JN	AD712JR	AD736AQ
AD705BQ	AD708SH	AD712KN	AD736AR
AD705JN	AD708SH/883B	AD712KR	AD736JNZ
AD705JR	AD708SQ	AD712SH	AD737AN
AD705KN	AD711AH	AD712SQ	AD737AR
AD705TQ	AD711AQ	AD712SQ/883B	AD737BQ
AD706AQ	AD711BH	AD712TH	AD741CH
AD706AR	AD711BQ	AD712TQ	AD741CN
AD706BQ	AD711CH	AD712TRZ-EP	AD741H
AD706JN	AD711CQ	AD713AQ	AD741JH
AD706JR	AD711JN	AD713BQ	AD741JN
AD706KN	AD711JR	AD713JN	AD741KH
AD706TQ	AD711KN	AD713JR	AD741KN
AD707AH	AD711KR	AD713JR-16	AD741LH
AD707AQ	AD711SH	AD713KN	AD741LN
AD707AR	AD711SQ	AD713SQ	AD741SH
AD707JN	AD711TH	AD713SQ/883B	AD743AN
AD707KN	AD711TQ	AD713TQ	AD743AQ
AD707KR	AD712AH	AD713TQ/883B	AD743AR
AD707TH	AD712AQ	AD734AN	AD743BQ

Multisim 14.0 Full Components

AD743JN	AD745JN	AD797BN	AD8009AR
AD743JR	AD745JR	AD797SQ	AD8009ARZ
AD743KN	AD745KN	AD8000YCPZ	AD8009JRT
AD743KR	AD745SQ	AD8000YCPZ-REEL	AD8010AN
AD743SQ	AD745SQ/883B	AD8000YRDZ	AD8010AR
AD743SQ/883B	AD746AQ	AD8001AN	AD8010AR-16
AD744AH	AD746BQ	AD8001AQ	AD8011AN
AD744AQ	AD746JN	AD8001AR	AD8011AR
AD744BH	AD746JR	AD8001ART	AD8012AR
AD744BQ	AD746SQ	AD8002AN	AD8012ARM
AD744CH	AD780AN	AD8002AR	AD8012ARMZ
AD744CQ	AD780AR	AD8002ARM	AD8014AR
AD744JN	AD780BN	AD8003ACPZ	AD8014ART
AD744JR	AD780BR	AD8003ACPZ-R2	AD8016ARB
AD744KN	AD795BH	AD8004AN	AD8016ARE
AD744KR	AD795JN	AD8004AR	AD8016AREZ
AD744SH	AD795JR	AD8004AR-14	AD8016ARP
AD744SQ	AD795JRZ	AD8004SQ	AD8017AR
AD744TH	AD795KN	AD8005AN	AD8018AR
AD744TH/883B	AD796AN	AD8005AR	AD8018ARU
AD744TQ	AD796AR	AD8005ART	AD8021AR
AD745AN	AD796BN	AD8007AKS	AD8021ARM
AD745AQ	AD796SQ/883B	AD8007AR	AD8021ARMZ
AD745AR	AD797AN	AD8008AR	AD8021ARZ
AD745BQ	AD797AR	AD8008ARM	AD8022AR

Multisim 14.0 Full Components

AD8022ARM	AD8031ARZ	AD8040AR	AD8055ARZ
AD8022ARMZ	AD8031BN	AD8040ARU	AD8056AN
AD8022ARZ	AD8031BNZ	AD8041AN	AD8056AR
AD8023AR	AD8031BR	AD8041AR	AD8056ARM
AD8024AR	AD8031BRZ	AD8042AN	AD8057AR
AD8027AR	AD8032AN	AD8042AR	AD8057ART
AD8027ART	AD8032ANZ	AD8044AN	AD8058AR
AD8027ARTZ	AD8032AR	AD8044AR	AD8058ARM
AD8027ARTZ-R2	AD8032ARM	AD8045ACP	AD8061AR
AD8027ARTZ-REEL	AD8032ARMZ	AD8045ACPZ-R2	AD8061ART
AD8027ARTZ-REEL7	AD8032ARZ	AD8045ARD	AD8062AR
AD8027ARZ	AD8032BN	AD8045ARDZ	AD8062ARM
AD8027ARZ-REEL	AD8032BNZ	AD8047AN	AD8062ARMZ
AD8027ARZ-REEL7	AD8032BR	AD8047AR	AD8062ARZ
AD8028ARMZ	AD8032BRZ	AD8048AN	AD8065AR
AD8028ARZ	AD8033AKS	AD8048AR	AD8065ART
AD8029AKS	AD8033AR	AD8051AR	AD8065ARTZ
AD8029AR	AD8034AR	AD8051ART	AD8065ARZ
AD8030AR	AD8034ART	AD8052AR	AD8066AR
AD8030ARJ	AD8036AN	AD8052ARM	AD8066ARM
AD8031AN	AD8036AR	AD8054AR	AD8066ARMZ
AD8031ANZ	AD8038AKS	AD8054ARU	AD8066ARZ
AD8031AR	AD8038AR	AD8055AN	AD8067ART
AD8031ART	AD8039AR	AD8055AR	AD8072ARM
AD8031ARTZ	AD8039ART	AD8055ART	AD8072JR

Multisim 14.0 Full Components

AD8079AR	AD8129ARZ-REEL	AD8139ACPZ-R2	AD8206WYRZ-R7
AD8079BR	AD8129ARZ-REEL7	AD8139ARD	AD8206WYRZ-RL
AD8091AR	AD812AN	AD8139ARDZ	AD8206YRZ
AD8091ART	AD812AR	AD813AN	AD8206YRZ-REEL
AD8092AR	AD8130AR	AD813AR	AD8206YRZ-REEL7
AD8092ARM	AD8130ARM	AD813AR-14	AD8207WBRZ
AD8099ACP	AD8131AR	AD8145YCPZ-R2	AD8207WBRZ-R7
AD8099ACPZ-R2	AD8131ARM	AD8146ACPZ-R2	AD8207WBRZ-RL
AD8099ARD	AD8131ARMZ	AD8147ACPZ-R2	AD8208WBRMZ
AD8099ARDZ	AD8131ARZ	AD8148ACPZ-R2	AD8208WBRZ
AD810AN	AD8132AR	AD815ARB-24	AD8209WBRMZ
AD810AR	AD8132ARM	AD817AN	AD820AN
AD810SN	AD8132ARMZ	AD817AR	AD820AR
AD810SR	AD8132ARZ	AD8184AN	AD820BN
AD811AN	AD8133ACP-R2	AD818AN	AD820BR
AD811AR-16	AD8137YCP	AD818AR	AD8210WYRZ
AD811AR-20	AD8137YCPZ	AD8205WHRZ	AD8210YRZ
AD811JR	AD8137YR	AD8205WHRZ-RL	AD8211YRJZ-R2
AD811SE/883B	AD8137YRZ	AD8205WYRZ	AD8214ARMZ
AD811SQ/883B	AD8138AR	AD8205WYRZ-R7	AD8216WYRZ
AD8129ARMZ	AD8138ARM	AD8205WYRZ-RL	AD8216WYRZ-R7
AD8129ARMZ-REEL	AD8138ARMZ	AD8205YRZ	AD8216WYRZ-RL
AD8129ARMZ-REEL7	AD8138ARZ	AD8205YRZ-R7	AD8216YRZ
AD8129ARZ	AD8139ACP	AD8205YRZ-RL	AD8216YRZ-R7
	AD8139ACPZ	AD8206WYRZ	AD8216YRZ-RL

Multisim 14.0 Full Components

AD8217BRMZ	AD8224ACPZ-RL	AD822AN	AD825AR-16
AD8217BRMZ-R7	AD8224ACPZ-WP	AD822AR	AD826AN
AD8217BRMZ-RL	AD8224BCPZ-R7	AD822ARM	AD826AR
AD8218BCPZ-RL	AD8224BCPZ-RL	AD822BN	AD8270ACPZ-R7
AD8218BRMZ	AD8224BCPZ-WP	AD822BR	AD8273ARZ
AD8218BRMZ-R7	AD8224HACPZ-R7	AD822SQ	AD8273ARZ-R7
AD8219BRMZ	AD8224HACPZ-RL	AD8235ACBZ-P7	AD8273ARZ-RL
AD8219BRMZ-RL	AD8224HACPZ-WP	AD8236ARMZ	AD8274ARMZ
AD8220ARMZ	AD8224HBCPZ-R7	AD8237ARMZ	AD8274ARMZ-R7
AD8220ARMZ-R7	AD8224HBCPZ-RL	AD8237ARMZ-R7	AD8274ARMZ-RL
AD8220ARMZ-RL	AD8224HBCPZ-WP	AD8237ARMZ-RL	AD8274ARZ
AD8220BRMZ	AD8225AR	AD823AN	AD8274ARZ-R7
AD8220BRMZ-R7	AD8226ARMZ	AD823AR	AD8274ARZ-RL
AD8220BRMZ-RL	AD8226ARZ	AD8244ARMZ	AD8275ARMZ
AD8220WARMZ	AD8226BRMZ	AD8244BRMZ	AD8275BRMZ
AD8220WARMZ-R7	AD8226BRZ	AD824AN	AD8276ARMZ
AD8220WARMZ-RL	AD8227ARMZ	AD824AR-14	AD8276ARZ
AD8221AR	AD8227ARZ	AD824AR-16	AD8276BRMZ
AD8221ARM	AD8227BRMZ	AD824BN	AD8276BRZ
AD8221BR	AD8227BRZ	AD8250ARMZ	AD8277ARZ
AD8222ACPZ-R7	AD8228ARMZ	AD8251ARMZ	AD8277BRZ
AD8222BCPZ-R7	AD8228ARZ	AD8253ARMZ	AD8278ARMZ
AD8222HACPZ-R7	AD8228BRMZ	AD8253ARMZ-R7	AD8278ARZ
AD8222HBCPZ-R7	AD8228BRZ	AD8253ARMZ-RL	AD8278BRMZ
AD8224ACPZ-R7	AD8229HDZ	AD825AR	AD8278BRZ

Multisim 14.0 Full Components

AD8279ARZ	AD8330ARQZ-RL	AD8337BCPZ-R2	AD8418BRMZ
AD8279BRZ	AD8331ARQZ	AD8337BCPZ-REEL	AD8418WBRMZ
AD827AQ	AD8331ARQZ-R7	AD8337BCPZ-REEL7	AD8418WBRZ
AD827JN	AD8331ARQZ-RL	AD8337BCPZ-WP	AD841JH
AD827JR-16	AD8332ACPZ-R2	AD8338ACPZ-R7	AD841JN
AD827SE/883B	AD8332ACPZ-R7	AD8338ACPZ-RL	AD841JQ
AD827SQ	AD8332ACPZ-RL	AD8397ARDZ	AD841KH
AD827SQ/883B	AD8332ARU	AD8397ARZ	AD841KN
AD828AN	AD8332ARU-REEL	AD840JN	AD841KQ
AD828AR	AD8332ARU-REEL7	AD840JQ	AD841SE
AD829AQ	AD8332ARUZ	AD840KN	AD841SH
AD829JN	AD8332ARUZ-R7	AD840KQ	AD841SQ
AD829JR	AD8332ARUZ-RL	AD840SE-883B	AD8420ARMZ
AD829SE/883B	AD8333ACPZ-REEL	AD840SQ	AD8420ARMZ-R7
AD829SQ	AD8333ACPZ-REEL7	AD840SQ-883B	AD8420ARMZ-RL
AD829SQ/883B	AD8333ACPZ-WP	AD8417BRMZ	AD8421ARMZ
AD8304ARU	AD8334ACPZ	AD8417WBRMZ	AD8421ARMZ-R7
AD830AN	AD8334ACPZ-REEL	AD8417WBRZ	AD8421ARMZ-RL
AD830JR	AD8334ACPZ-REEL7	AD8417WHRMZ	AD8421ARZ
AD8310ARM	AD8335ACPZ	AD8417WHRZ	AD8421ARZ-R7
AD8330ACPZ-R2	AD8335ACPZ-REEL	AD8418ABRMZ	AD8421ARZ-RL
AD8330ACPZ-R7	AD8335ACPZ-REEL7	AD8418AWBRMZ	AD8421BRMZ
AD8330ACPZ-RL	AD8336ACPZ-R7	AD8418AWBRZ	AD8421BRMZ-R7
AD8330ARQZ	AD8336ACPZ-RL	AD8418AWHRMZ	AD8421BRMZ-RL
AD8330ARQZ-R7	AD8336ACPZ-WP	AD8418AWHRZ	AD8421BRZ

Multisim 14.0 Full Components

AD8421BRZ-R7	AD842JH	AD843JN	AD846AQ
AD8421BRZ-RL	AD842JN	AD843JR	AD846BQ
AD8421TRMZ-EP	AD842JQ	AD843JR-16	AD846SQ
AD8421TRMZ-EP-R7	AD842JR	AD843KN	AD8475ACPZ-R7
AD8422ARMZ	AD842KH	AD843SE	AD8475ACPZ-RL
AD8422ARMZ-R7	AD842KN	AD843SE/883B	AD8475ACPZ-WP
AD8422ARMZ-RL	AD842KQ	AD843SH	AD8475ARMZ
AD8422ARZ	AD842SE	AD843SQ	AD8475ARMZ-R7
AD8422ARZ-R7	AD842SH	AD843SQ/883B	AD8475ARMZ-RL
AD8422ARZ-RL	AD842SQ	AD844AN	AD8475BRMZ
AD8422BRMZ	AD8436ACPZ-R7	AD844AQ	AD8475BRMZ-R7
AD8422BRMZ-R7	AD8436ACPZ-RL	AD844BQ	AD8475BRMZ-RL
AD8422BRMZ-RL	AD8436ACPZ-WP	AD844JRZ-16	AD8476ACPZ-R7
AD8422BRZ	AD8436ARQZ	AD844SQ	AD8476ACPZ-RL
AD8422BRZ-R7	AD8436ARQZ-R7	AD8450ASTZ	AD8476ACPZ-WP
AD8422BRZ-RL	AD8436ARQZ-RL	AD8451ASTZ	AD8476ARMZ
AD8426ACPZ-R7	AD8436BRQZ	AD845AQ	AD8476ARMZ-R7
AD8426ACPZ-WP	AD8436BRQZ-R7	AD845BQ	AD8476ARMZ-RL
AD8426BCPZ-R7	AD8436BRQZ-RL	AD845JN	AD8476BCPZ-R7
AD8426BCPZ-WP	AD8436JCPZ-R7	AD845JR	AD8476BCPZ-RL
AD8429ARZ	AD8436JCPZ-RL	AD845JR-16	AD8476BCPZ-WP
AD8429ARZ-R7	AD8436JCPZ-WP	AD845KN	AD8476BRMZ
AD8429BRZ	AD843AQ	AD845SQ	AD8476BRMZ-R7
AD8429BRZ-R7	AD843BH	AD845SQ/883B	AD8476BRMZ-RL
	AD843BQ	AD846AN	AD8479ARZ

Multisim 14.0 Full Components

AD8479ARZ-RL	AD8496CRMZ-R7	AD8513ARU	AD8541ARZ
AD8479BRZ	AD8497ARMZ	AD8515AKS	AD8542AR
AD8479BRZ-RL	AD8497ARMZ-R7	AD8515ART	AD8542ARM
AD847AQ	AD8497CRMZ	AD8517ART	AD8542ARU
AD847AR	AD8497CRMZ-R7	AD8519AKS	AD8544AR
AD847JN	AD849AQ	AD8519AR	AD8544ARU
AD847JR	AD849JN	AD8519ART	AD8546ARMZ
AD847SQ	AD849JR	AD8527AR	AD8548ARZ
AD847SQ/883B	AD849SQ	AD8529AR	AD8548ARZ-R7
AD848AQ	AD849SQ/883B	AD8529ARM	AD8548ARZ-RL
AD848JN	AD8500AKSZ	AD8531AKS	AD8551AR
AD848JR	AD8502ARJZ	AD8531AR	AD8551ARM
AD848SQ	AD8504ARUZ	AD8532AR	AD8552AR
AD848SQ/883B	AD8505ACBZ-R7	AD8532ARM	AD8552ARU
AD8494ARMZ	AD8505ARJZ-RL	AD8532ARU	AD8554AR
AD8494ARMZ-R7	AD8506ARMZ	AD8534AR	AD8554ARU
AD8494CRMZ	AD8508ACBZ-REEL	AD8534ARU	AD8561AN
AD8494CRMZ-R7	AD8508ARUZ	AD8538ARZ	AD8561AR
AD8495ARMZ	AD8510AR	AD8538AUJZ	AD8561ARU
AD8495ARMZ-R7	AD8510ARM	AD8538AUJZ-R2	AD8564AN
AD8495CRMZ	AD8510BR	AD8539ARMZ	AD8564AR
AD8495CRMZ-R7	AD8512AR	AD8539ARZ	AD8565AKS
AD8496ARMZ	AD8512ARM	AD8541AKS	AD8565AKSZ
AD8496ARMZ-R7	AD8512BR	AD8541AR	AD8571AR
AD8496CRMZ	AD8513AR	AD8541ART	AD8571ARM

Multisim 14.0 Full Components

AD8572AR	AD8607AR	AD8618AR	AD8630ARZ
AD8572ARU	AD8607ARM-REEL	AD8618ARU	AD8630WARZ-RL
AD8574AR	AD8608AR	AD8619ARUZ	AD8631ART
AD8574ARU	AD8608ARU	AD8619ARZ	AD8631ARTZ
AD8591ART	AD8609AR	AD8620AR	AD8632AR
AD8592ARM	AD8609ARU	AD8620BR	AD8632ARM
AD8594AR	AD8610AR	AD8622ARMZ	AD8632ARMZ
AD8594ARU	AD8610ARM	AD8622ARZ	AD8632ARZ
AD8597ACPZ-R2	AD8610ARZ	AD8624ACPZ-R2	AD8638ARJZ
AD8597ARZ	AD8610BR	AD8624ARUZ	AD8638ARZ
AD8599ARZ	AD8611AR	AD8625ARUZ	AD8639ACPZ-R2
AD8601ART	AD8611ARM	AD8625ARZ	AD8639ARMZ
AD8602AR	AD8612ARU	AD8626ARMZ	AD8639ARZ
AD8602ARM	AD8613AKSZ	AD8626ARZ	AD8639WARZ
AD8603AUJZ	AD8613AUJZ	AD8627AKS	AD8641AKSZ
AD8604AR	AD8614ART	AD8627AKSZ	AD8641AKSZ-R2
AD8604ARQZ	AD8615AUJZ	AD8627AR	AD8641ARZ
AD8604ARUZ	AD8616AR	AD8627ARZ	AD8642ARMZ
AD8604DRU	AD8616ARM	AD8628AR	AD8642ARZ
AD8604DRZ	AD8617ACPZ-R2	AD8628ART	AD8643ACPZ-R2
AD8605ACB	AD8617ARMZ	AD8628AUJ	AD8643ARZ
AD8605ART	AD8617ARZ	AD8629ARMZ	AD8644AR
AD8606ACBZ-REEL	AD8617WARMZ-REEL	AD8629ARZ	AD8644ARU
AD8606AR		AD8629WARZ-RL	AD8646ARMZ
AD8606ARM-REEL	AD8617WARZ-RL	AD8630ARUZ	AD8646ARZ

Multisim 14.0 Full Components

AD8646WARMZ-RL	AD8664ARZ	AD8694ARUZ	AD9630AN
AD8646WARZ-RL	AD8667ARMZ	AD8694ARZ	AD9630AQ
AD8648ARUZ	AD8667ARZ	AD8698AR	AD9630AR
AD8648ARZ	AD8669ARUZ	AD8698ARM	AD9631AN
AD8648WARUZ	AD8669ARZ	AD9218_FP48	AD9631AR
AD8651AR	AD8671AR	AD9610TH	AD9632AN
AD8651ARM	AD8671ARM	AD9610TH/883B	AD9632AR
AD8655ARMZ	AD8671ARMZ	AD9617AQ	AD9841A-LQFP(48)
AD8655ARZ	AD8672AR	AD9617BQ	AD9842A-LQFP(48)
AD8656ARMZ	AD8672ARM	AD9617JN	ADA4000-1ARZ
AD8656ARZ	AD8672ARMZ	AD9617JR	ADA4000-1AUJZ
AD8657ACPZ-RL	AD8674AR	AD9617SQ	ADA4000-1AUJZ-RL
AD8657ARMZ	AD8674ARU	AD9617TQ	ADA4000-2ARMZ
AD8659ACPZ-R7	AD8675ARMZ	AD9618AQ	ADA4000-2ARZ
AD8659ACPZ-RL	AD8675ARZ	AD9618BQ	ADA4000-4ARUZ
AD8659ARZ	AD8676ARMZ	AD9618JN	ADA4000-4ARZ
AD8659ARZ-R7	AD8676ARZ	AD9618JR	ADA4001-2ARZ
AD8659ARZ-RL	AD8676BRMZ	AD9618SQ	ADA4001-2ARZ-R7
AD8661ACPZ-R2	AD8676BRZ	AD9618TQ	ADA4001-2ARZ-RL
AD8661ARZ	AD8677ARZ	AD9620AD	ADA4004-1ARJZ-R2
AD8662ARMZ	AD8677AUJZ-R2	AD9620SD	ADA4004-1ARJZ-R7
AD8662ARZ	AD8691AKSZ	AD9621AN	ADA4004-1ARJZ-RL
AD8663ACPZ	AD8691AUJZ	AD9622AN	ADA4004-1ARZ
AD8663ARZ	AD8692ARMZ	AD9623AN	ADA4004-1ARZ-R7
AD8664ARUZ	AD8692ARZ	AD9624AN	ADA4004-1ARZ-RL

Multisim 14.0 Full Components

ADA4004-2ARMZ	ADA4077-1ARMZ	ADA4091-4ACPZ-R2	ADA4610-2ACPZ-RL
ADA4004-2ARMZ-R7	ADA4077-1ARZ	ADA4091-4ARUZ	ADA4610-2ARMZ
ADA4004-2ARMZ-RL	ADA4077-1BRZ	ADA4092-4ARUZ	ADA4610-2ARMZ-R7
ADA4004-2ARZ	ADA4077-2ARMZ	ADA4096-2ACPZ-R7	ADA4610-2ARMZ-RL
ADA4004-2ARZ-R7	ADA4077-2ARMZ-R7	ADA4096-2ARMZ	ADA4610-2ARZ
ADA4004-2ARZ-RL	ADA4077-2ARMZ-RL	ADA4096-2WARMZ-R7	ADA4610-2ARZ-R7
ADA4004-4ACPZ-R2	ADA4077-2ARZ	ADA4096-2WARMZ-RL	ADA4610-2ARZ-RL
ADA4004-4ACPZ-R7	ADA4077-2ARZ-R7	ADA4096-4ACPZ-R7	ADA4610-2BRZ
ADA4004-4ACPZ-RL	ADA4077-2ARZ-RL	ADA4096-4ARUZ	ADA4610-2BRZ-R7
ADA4004-4ARZ	ADA4077-2BRZ	ADA4500-2ACPZ-R7	ADA4610-2BRZ-RL
ADA4004-4ARZ-R7	ADA4077-2BRZ-R7	ADA4500-2ACPZ-RL	ADA4627-1ACPZ-RL
ADA4004-4ARZ-RL	ADA4077-2BRZ-RL	ADA4500-2ARMZ	ADA4627-1ARZ
ADA4051-1AKSZ-R2	ADA4077-4ARUZ	ADA4500-2ARMZ-R7	ADA4627-1BRZ
ADA4051-1ARJZ-R2	ADA4077-4ARZ	ADA4500-2ARMZ-RL	ADA4637-1ACPZ-R2
ADA4051-2ACPZ-R2	ADA4084-2ARMZ	ADA4505-1ACBZ-R7	ADA4637-1ARZ
ADA4051-2ARMZ	ADA4084-2ARMZ-R7	ADA4505-1ARJZ-R2	ADA4637-1BRZ
ADA4062-2ACPZ-RL	ADA4084-2ARMZ-RL	ADA4505-2ACBZ-RL	ADA4638-1ACPZ-R7
ADA4062-2ARMZ	ADA4084-2ARZ	ADA4505-2ARMZ	ADA4638-1ACPZ-RL
ADA4062-2ARZ	ADA4084-2ARZ-R7	ADA4505-4ACBZ-RL	ADA4638-1ARZ
ADA4062-2BRZ	ADA4084-2ARZ-RL	ADA4505-4ARUZ	ADA4638-1ARZ-R7
ADA4062-4ACPZ-R2	ADA4091-2ACPZ-R2	ADA4528-1ARMZ	ADA4638-1ARZ-RL
ADA4062-4ARUZ	ADA4091-2ARZ	ADA4610-2ACPZ-R7	ADA4661-2ACPZ-R7
ADA4075-2ACPZ-RL			ADA4661-2ACPZ-RL
ADA4075-2ARZ			ADA4661-2ARMZ

Multisim 14.0 Full Components

ADA4661-2ARMZ-R7	ADA4817-1ARDZ-R7	ADA4853-3YRUZ	ADA4895-2ARMZ-RL
ADA4661-2ARMZ-RL	ADA4817-1ARDZ-RL	ADA4855-3YCPZ-R2	ADA4896-2ACPZ-R2
ADA4665-2ARMZ	ADA4817-2ACPZ-R2	ADA4857-1YCPZ-R2	ADA4896-2ACPZ-R7
ADA4665-2ARZ	ADA4817-2ACPZ-R7	ADA4857-1YRZ	ADA4896-2ACPZ-RL
ADA4666-2ACPZ-R7	ADA4817-2ACPZ-RL	ADA4857-2YCPZ-R2	ADA4896-2ARMZ
ADA4666-2ACPZ-RL	ADA4841-1YRZ	ADA4858-3ACPZ-R2	ADA4896-2ARMZ-R7
ADA4666-2ARMZ	ADA4850-1YCPZ	ADA4860-1YRJZ-R2	ADA4896-2ARMZ-RL
ADA4666-2ARMZ-R7	ADA4850-1YCPZ-R2	ADA4860-1YRJZ-RL	ADA4896-2ARMZ-RL
ADA4666-2ARMZ-RL	ADA4850-2YCPZ-R2	ADA4860-1YRJZ-RL7	ADA4897-1ARJZ-R2
ADA4691-2ACBZ-R7	ADA4850-2YCPZ-RL	ADA4861-3YRZ	ADA4897-1ARZ
ADA4691-2ACPZ-R7	ADA4851-1WYRJZ-R7	ADA4861-3YRZ-RL	ADA4897-1SRJZ-EPR7
ADA4691-4ACPZ-R7	ADA4851-1YRJZ-R2	ADA4861-3YRZ-RL7	ADA4897-2ARMZ
ADA4692-2ACPZ-R7	ADA4851-1YRJZ-RL	ADA4870ARRZ	ADA4897-2TRMZ-EP
ADA4692-2ARZ	ADA4851-2WYRMZ	ADA4891-1ARZ	ADA4898-1YRDZ
ADA4692-4ARUZ	ADA4851-2YRMZ-RL	ADA4891-2ARMZ	ADA4898-2YRDZ
ADA4700-1ARDZ	ADA4851-4WYRUZ	ADA4891-2ARZ	ADA4899-1YCPZ
ADA4805-1AKSZ-R2	ADA4851-4YRUZ	ADA4891-3ARUZ	ADA4899-1YCPZ-R2
ADA4805-1ARJZ-R2	ADA4851-4YRUZ-RL	ADA4891-3ARZ	ADA4899-1YRDZ
ADA4817-1ACPZ-R2	ADA4853-1AKSZ-R2	ADA4891-4ARUZ	ADA4922-1ACPZ-R2
ADA4817-1ACPZ-R7	ADA4853-2YCPZ-R2	ADA4891-4ARZ	ADA4922-1ARDZ
ADA4817-1ACPZ-RL	ADA4853-3WYCPZ-R7	ADA4895-2ARMZ	ADA4927-1YCPZ-R2
ADA4817-1ARDZ	ADA4853-3YCPZ-R2	ADA4895-2ARMZ-R7	ADA4927-2YCPZ
			ADA4930-1YCPZ-R2

Multisim 14.0 Full Components

ADA4930-2YCPZ-R2	ADG1211YCPZ-500RL7	ADG408TQ	ADG426BRS
ADA4932-1YCPZ-R2	ADG1211YRUZ	ADG409BN	ADG441ABN
ADA4932-2YCPZ-R2	ADG1212YCPZ-500RL7	ADG409BR	ADG441ABR
ADA4937-1YCPZ-R2	ADG1212YRUZ	ADG409BRU	ADG441BN
ADA4937-2YCPZ-R2	ADG1213YCPZ-500RL7	ADG409TQ	ADG441BR
ADA4938-1ACPZ-R2	ADG1213YRUZ	ADG411	ADG441TQ
ADA4938-2ACPZ-R2	ADG1236YCPZ-500RL7	ADG411BN	ADG442BN
ADA4939-1YCPZ-R2	ADG1236YRUZ	ADG411BR	ADG442SQ
ADA4939-2YCPZ-R2	ADG1311YRUZ	ADG411BRU	ADG444
ADA4940-1ACPZ-R2	ADG1311YRZ	ADG411BRUZ	ADG444ABN
ADA4940-1ACPZ-R7	ADG1312YRUZ	ADG411BRZ	ADG444ABR
ADA4940-1ACPZ-RL	ADG1313YRUZ	ADG411TQ	ADG444BN
ADA4940-2ACPZ-R2	ADG406BN	ADG412	ADG444BR
ADA4940-2ACPZ-R7	ADG406BP	ADG412BN	ADG444S
ADA4940-2ACPZ-RL	ADG407BN	ADG412BR	ADG508FBN
ADA4941-1YCPZ-RL	ADG407BP	ADG412BRU	ADG508FBNZ
ADA4941-1YRZ	ADG408	ADG412BRUZ	ADG508FBRN
ADA4950-1YCPZ-R2	ADG408BN	ADG412BRZ	ADG508FBRUZ
ADA4950-2YCPZ-R2	ADG408BR	ADG412TQ	ADG508FBRW
ADA4960-1ACPZ-R2	ADG408BRU	ADG413BN	ADG508FTQ
ADC		ADG413BNZ	ADG509FBN
ADC16		ADG413BR	ADG509FBRN
ADD_FULL		ADG413BRUZ	ADG509FBRUZ
ADD_FULL4_FCR		ADG413BRZ	ADG509FBRW
ADD_HALF		ADG426BN	ADG509FBRWZ

Multisim 14.0 Full Components

ADG509FTQ	ADG608BRU	ADG702BRTZ-REEL	ADG787BCPZ-REEL
ADG511BN	ADG608TRU	ADG711BR	ADG787BRMZ
ADG511BR	ADG609BN	ADG711BRU	ADG801BRM
ADG511PM5	ADG609BR	ADG712BR	ADG801BRT-500RL7
ADG511TQ	ADG609BRU	ADG712BRU	ADG802BCBZ-REEL7
ADG512BN	ADG609BRUZ	ADG713BR	ADG802BRM
ADG512BR	ADG609BRZ	ADG713BRU	ADG802BRT-500RL7
ADG512PM5	ADG611YRUZ	ADG719BRM	ADG811YCPZ-REEL
ADG512TQ	ADG611YRZ	ADG719BRT-REEL	ADG811YRU
ADG513BN	ADG612WYRUZ-REEL	ADG721ACPZ-REEL	ADG812YRU
ADG513BR	ADG612YRUZ	ADG721BRM	ADG813YRU
ADG513PM5	ADG613YRUZ	ADG722ACPZ-REEL	ADG819BCB
ADG513TQ	ADG658YCPZ	ADG722BRM	ADG819BRM
ADG528F	ADG658YRQ	ADG723ACPZ-REEL	ADG819BRT
ADG528FBN	ADG658YRU	ADG723BRM	ADG820BRM
ADG528FBP	ADG659YCPZ	ADG741BKSZ5-REEL	ADG820BRT
ADG528FTQ	ADG659YRQ	ADG741BKSZ-REEL	ADG821BRM
ADG601BRMZ	ADG659YRU	ADG742BKSZ5-REEL	ADG822BRM
ADG601BRTZ-REEL	ADG663BRU	ADG742BKSZ-R2	ADG823BRM
ADG602BRM	ADG701BRJ-500RL7	ADG749BKSZ-REEL	ADG839YKSZ-500RL7
ADG602BRTZ-REEL	ADG701BRM	ADG779BKSZ-R2	ADG841YKSZ-500RL7
ADG604YRU	ADG701BRTZ-REEL	ADG781BCP	
ADG604YRUZ	ADG702BRJ-REEL7	ADG782BCP	
ADG608BN	ADG702BRM	ADG783BCP	
ADG608BR		ADG787BCBZ-REEL	

Multisim 14.0 Full Components

ADG842YKSZ-500RL7	ADSP-2103-PQFP(80)	ADSP-2163-PQFP(80)	ALPHA_NUMERIC_COM_A_ORANGE
ADG849YKSZ-500RL7	ADSP-2103-TQFP(80)	ADSP-2163-TQFP(80)	ALPHA_NUMERIC_COM_A_RED
ADG859BRYZ-REEL	ADSP-2105-PLCC(68)	ADSP-2164-PLCC(68)	ALPHA_NUMERIC_COM_A_YELLOW
ADG859YRYZ-REEL			
ADG884BCBZ-REEL	ADSP-2111-PGA(100)	ADSP-2164-PQFP(80)	ALPHA_NUMERIC_COM_K_BLUE
ADG884BCPZ-REEL	ADSP-2111-PQFP(100)	ADSP-2164-TQFP(80)	ALPHA_NUMERIC_COM_K_GREEN
ADG884BRMZ			
ADR3425ARJZ-R2	ADSP-2115-PLCC(68)	ADSP-2191M-LQFP(144)	ALPHA_NUMERIC_COM_K_ORANGE
ADR3425ARJZ-R7	ADSP-2115-PQFP(80)	ADTL082ARMZ	ALPHA_NUMERIC_COM_K_RED
ADR5040AKSZ-R2		ADTL082ARZ	
ADR5040ARTZ-R2	ADSP-2115-TQFP(80)	ADTL082JR	ALPHA_NUMERIC_COM_K_YELLOW
ADR5040BKSZ-R2			
ADR5040BRTZ-R2	ADSP-2161-PLCC(68)	ADTL082JRZ	ALTERA-BYTEBLASTER-HDR
ADS8320EB	ADSP-2161-PQFP(80)	ADTL084ARZ	ALU_4BIT
ADS8322YB		ADTL084JR	AM_VOLTAGE
ADS8364Y	ADSP-2161-TQFP(80)	ADTL084JRZ	AM29520ADC
ADSP-2101-PGA(68)			
ADSP-2101-PLCC(68)	ADSP-2162-PLCC(68)	ADZS-BRKOUT-EX3	AM29520ADCB
		AIR_NC	AM29520AJC
ADSP-2101-PQFP(80)	ADSP-2162-PQFP(80)	AIR_NO	AM29520ALC
ADSP-2101-TQFP(80)	ADSP-2162-TQFP(80)	ALPHA_NUMERIC_COM_A_BLUE	AM29520APC
			AM29520APCB
ADSP-2103-PLCC(68)	ADSP-2163-PLCC(68)	ALPHA_NUMERIC_COM_A_GREEN	AM29521ADC
			AM29521ADCB

Multisim 14.0 Full Components

AM29521AJC	AND2	ASP-134488-01	AUIRF7648M2TR
AM29521ALC	AND2	ASP-134603-01	AUIRF7669L2TR
AM29521APC	AND3	ASP-134604-01	AUIRF7734M2TR
AM29521APCB	AND3	ASP-134606-01	AUIRF7736M2TR
AM29LV800BB-70EI	AND4	ASSR-V621-002E	AUIRF7737L2TR
AMMETER_H	AND4	ASSR-V621-302E	AUIRF7738L2TR
AMMETER_HR	AND5	ASSR-V622-002E	AUIRF7739L2TR
AMMETER_V	AND5	ASSR-V622-302E	AUIRFR4292
AMMETER_VR	AND6	ATF750C-10PC	AUIRFR4292TRL
AMP01AX	AND6	ATF750C-10XC	AUIRFR4292TRR
AMP01BX	AND7	ATF750C-15PC	AUIRFS6535
AMP01EX	AND7	ATF750C-15XC	AUIRFS6535TRL
AMP01FX	AND8	ATF750CL-15PC	AUIRFS8407
AMP01GS	AND8	ATF750CL-15XC	AUIRFS8407TRL
AMP02AZ	ANTI_PLUG	ATP207-TL-H	AUIRFS8408
AMP02EP	ARBITRARY_LAPLAC E_FUNCTION	ATP301-TL-H	AUIRFS8408TRL
AMP02FP		ATP405-TL-H	AUIRFS8408TRR
AMP02FS	ARBITRARY_LOGIC_ BLOCK_16_16	ATV2500BL-20JI	AUIRFSL6535
AMP04EP	ARBITRARY_LOGIC_ BLOCK_4_4	ATV2500BQ-20JC	AUIRFSL8408
AMP04ES		AUIRF2903ZL	AUIRFU4292
AMP04FP	ARBITRARY_LOGIC_ BLOCK_8_8	AUIRF2903ZS	AUIRFZ44VZS
AMP04FS		AUIRF3004WL	AUIRGDC0250
ANALOG_SWITCH_ VIRTUAL	ARBITRARY_SPICE_ BLOCK	AUIRF7303QTR	AUIRGP4063D
AND_OR_I	ARM-14-HDR	AUIRF7640S2TR	AUIRGP4063D-E
	ARM-20-HDR	AUIRF7647S2TR	AUIRGP4066D1

Multisim 14.0 Full Components

AUIRGP4066D1-E	BA316	BAR_LED_GREEN_T EN	BAR63-04W
AUIRGP50B60PD1	BA317		BAR63-05
AUIRGP50B60PD1E	BA318	BAR_LED_ORANGE	BAR63-05W
AUIRGPS4067D1	BA423	BAR_LED_ORANGE _FOUR	BAR63-06
AUIRGR4045D	BA423L	BAR_LED_ORANGE	BAR63-06W
AUIRGR4045DTR	BA481	_TEN	BAR64-02V
AUIRGR4045DTRL	BA482	BAR_LED_RED	BAR64-03W
AUIRGR4045DTRR	BA483	BAR_LED_RED_FOU R	BAR64-04
AUIRGU4045D	BA484	BAR_LED_RED_TEN	BAR64-04W
AUIRLS3034-7P	BA592	BAR_LED_YELLOW	BAR64-05W
AUIRLS3034-7TRL	BA595	BAR_LED_YELLOW_ FOUR	BAR64-06W
AUIRLS3114Z	BA682		BAR65-03W
AUIRLS3114ZTRL	BA683	BAR_LED_YELLOW_ TEN	BAR67-02V
AVR-JTAG-HDR	BA885		BAR74
B6S-E3/80	BA892	BAR14-1	BAR81W
BA157GP	BA895	BAR15-1	BAR88-02V
BA158GP	BAL74	BAR16-1	BAR99
BA159-E3/54	BAL99	BAR50-02L	BAS101
BA159GP	BAR_LED_BLUE	BAR50-02V	BAS101S
BA220	BAR_LED_BLUE_FO UR	BAR61	BAS11
BA221		BAR63-02L	BAS116
BA223	BAR_LED_BLUE_TE N	BAR63-02V	BAS116H
BA281	BAR_LED_GREEN	BAR63-02W	BAS116LT1G
BA314	BAR_LED_GREEN_F OUR	BAR63-03W	BAS116T
BA315		BAR63-04	BAS116TT1G

Multisim 14.0 Full Components

BAS125-04W	BAS21AW	BAS40-05V	BAS70-05
BAS125-05W	BAS21H	BAS40-05W	BAS70-05W
BAS125-07W	BAS21HT1G	BAS40-06	BAS70-06
BAS140W	BAS21J	BAS40-06W	BAS70-06W
BAS15	BAS21M3T5G	BAS40-07	BAS70-07
BAS16	BAS21SLT1G	BAS40-07V	BAS70-07S
BAS16-02L	BAS21SW	BAS40-07W	BAS70-07V
BAS16DXV6T1G	BAS21TMR6T1G	BAS40H	BAS70H
BAS16H	BAS21U	BAS40L	BAS70L
BAS16J	BAS21VD	BAS40W	BAS70VV
BAS16L	BAS21W	BAS40XY	BAS70W
BAS16LD	BAS28	BAS416	BAS70XY
BAS16M3T5G	BAS29	BAS45	BAS716
BAS16P2T5G	BAS3010B-03W	BAS45A	BAS81
BAS16T	BAS3020B	BAS45AL	BAS82
BAS16VV	BAS31	BAS45L	BAS83
BAS16VY	BAS316	BAS516	BAS85
BAS16W	BAS32	BAS521	BAS86
BAS17	BAS321	BAS56	BAT120A
BAS170W	BAS32L	BAS70	BAT120C
BAS19	BAS35	BAS70-02L	BAT120S
BAS20	BAS40	BAS70-02W	BAT15-02LRH
BAS20LT1G	BAS40-02L	BAS70-04	BAT15-03W
BAS21	BAS40-04	BAS70-04LT1G	BAT15-05W
BAS21AVD	BAS40-05	BAS70-04W	BAT15-099

Multisim 14.0 Full Components

BAT160A	BAT54CV	BAT64-05	BAT83
BAT160C	BAT54CW	BAT64-05W	BAT85
BAT160S	BAT54H	BAT64-06	BAT854AW
BAT165	BAT54J	BAT64-06W	BAT854CW
BAT17	BAT54L	BAT68	BAT854SW
BAT17-04	BAT54M3T5G	BAT68-04	BAT854W
BAT17-05	BAT54S	BAT68-04W	BAT86
BAT17-05W	BAT54SW	BAT68-06	BAT960
BAT17-06W	BAT54T	BAT68-06W	BAV10
BAT17-07	BAT54VV	BAT720	BAV100
BAT18	BAT54W	BAT721	BAV101
BAT18-04	BAT54WT1G	BAT721A	BAV102
BAT18-05	BAT54XY	BAT721C	BAV103
BAT24-02LS	BAT60A	BAT721S	BAV105
BAT240A	BAT60B	BAT74	BAV170
BAT46WH	BAT62	BAT74S	BAV18
BAT46WJ	BAT62-02L	BAT74V	BAV19
BAT54	BAT62-02W	BAT754	BAV199
BAT54A	BAT62-03W	BAT754A	BAV199W
BAT54AW	BAT62-07W	BAT754C	BAV20
BAT54C	BAT63-07W	BAT754L	BAV21
BAT54CLT1	BAT64	BAT754S	BAV23
BAT54CLT1G	BAT64-02W	BAT760	BAV23A
BAT54CLT3G	BAT64-04	BAT81	BAV23C
BAT54CM	BAT64-04W	BAT82	BAV23S

Multisim 14.0 Full Components

BAV45	BAW156	BB241	BB804
BAV70	BAW56	BB249	BB809
BAV70DXV6T5G	BAW56LT1	BB405B	BB811
BAV70LT1	BAW56LT1G	BB417	BB814
BAV70LT1G	BAW56LT3G	BB439	BB833
BAV70LT3G	BAW56M	BB515	BB837
BAV70M	BAW56M3T5G	BB535	BB857
BAV70M3T5G	BAW56S	BB545	BB909A
BAV70S	BAW56T	BB555	BB909B
BAV70T	BAW56TT1G	BB555-02V	BB910
BAV70TT1G	BAW56W	BB565	BB911
BAV70W	BAW62	BB565-02V	BB914
BAV74	BAX12	BB619	BBY31
BAV74LT1	BAX14	BB620	BBY39
BAV74LT1G	BAX18	BB639	BBY40
BAV756S	BAY80	BB639C	BBY42
BAV99	BB112	BB640	BBY51-02W
BAV99LT1	BB119	BB644	BBY51-03W
BAV99LT1G	BB130	BB659	BBY52-02L
BAV99LT3	BB204B	BB659C	BBY52-02W
BAV99LT3G	BB204G	BB659C-02V	BBY53-02L
BAV99S	BB212	BB664	BBY53-02V
BAV99W	BB215	BB664-02V	BBY53-02W
BAW101	BB219	BB689	BBY53-03W
BAW101S	BB240	BB689-02V	BBY53-05W

Multisim 14.0 Full Components

BBY55-02V	BC213AP	BC54-10PA	BC68-25PA
BBY55-03W	BC237BP	BC54-16PA	BC68PA
BBY56-02W	BC238BP	BC546BP	BC69-16PA
BBY56-03W	BC239BP	BC547BG	BC69-25PA
BBY57-02V	BC264A	BC547BP	BC69PA
BBY57-02W	BC264B	BC547BRL1G	BC807
BBY57-05W	BC264C	BC547BZL1G	BC807-16
BBY58-02V	BC264D	BC548BP	BC807-16LT1G
BBY58-02W	BC307AP	BC549BP	BC807-16LT3G
BBY58-03W	BC308AP	BC54PA	BC807-16W
BBY58-05W	BC337AP	BC550BP	BC807-25
BBY58-06W	BC338AP	BC55-10PA	BC807-25LT1G
BBY62	BC413BP	BC55-16PA	BC807-25LT3G
BBY65-02V	BC414BP	BC556AP	BC807-25QA
BBY66-02V	BC415AP	BC557AP	BC807-25W
BBY66-05W	BC416AP	BC557BG	BC807-40
BC107BP	BC51-10PA	BC557BRL1G	BC807-40LT1G
BC108BP	BC51-16PA	BC557BZL1G	BC807-40LT3G
BC109BP	BC51PA	BC558AP	BC807-40QA
BC177AP	BC52-10PA	BC559AP	BC807-40W
BC178AP	BC52-16PA	BC55PA	BC807DS
BC182BP	BC52PA	BC560AP	BC807W
BC183BP	BC53-10PA	BC56-10PA	BC808-16
BC184BP	BC53-16PA	BC56-16PA	BC817
BC212AP	BC53PA	BC56PA	BC817-16

Multisim 14.0 Full Components

BC817-16W	BC846BPN	BC847BPN	BC850CW
BC817-25	BC846BS	BC847BS	BC856
BC817-25LT1	BC846BT	BC847BT	BC856A
BC817-25LT1G	BC846BW	BC847BV	BC856ALT1G
BC817-25LT3G	BC846DS	BC847BVN	BC856AT
BC817-25QA	BC846S	BC847BW	BC856AW
BC817-25W	BC846T	BC847C	BC856B
BC817-40	BC846W	BC847CDXV6T1G	BC856BDW1T1G
BC817-40QA	BC847	BC847CM	BC856BDW1T3G
BC817-40W	BC847A	BC847CMB	BC856BS
BC817DPN	BC847AM	BC847CT	BC856BT
BC817DS	BC847AMB	BC847CTT1G	BC856BW
BC817W	BC847AT	BC847CW	BC856BWT1G
BC846	BC847AW	BC847DS	BC856S
BC846A	BC847B	BC847T	BC856T
BC846ALT1G	BC847BDW1T1G	BC847W	BC856W
BC846ALT3G	BC847BDW1T3	BC848B	BC857
BC846AT	BC847BDW1T3G	BC848W	BC857A
BC846AW	BC847BM	BC849B	BC857AM
BC846B	BC847BMB	BC849BW	BC857AMB
BC846BDW1T1G	BC847BPDW1T1	BC849C	BC857AT
BC846BLT1G	BC847BPDW1T1G	BC849CW	BC857AW
BC846BLT3G	BC847BPDW1T2G	BC850B	BC857B
BC846BMB	BC847BPDW1T3G	BC850BW	BC857BDW1T1G
BC846BPDW1T1G	BC847BPDV6T1G	BC850C	BC857BM

Multisim 14.0 Full Components

BC857BMB	BC868	BCP53-16	BCR08PN
BC857BS	BC868-25	BCP54	BCR108
BC857BT	BC869	BCP54-10	BCR108S
BC857BV	BC869-16	BCP54-16	BCR108W
BC857BW	BC869-25	BCP55	BCR10PN
BC857C	BCD_7SEG_DCD	BCP55-10	BCR112
BC857CM	BCM61B	BCP55-16	BCR112W
BC857CMB	BCM62B	BCP56	BCR116
BC857CT	BCM847BS	BCP56-10	BCR116S
BC857CW	BCM847BV	BCP56-10T1	BCR116W
BC857T	BCM847DS	BCP56-10T1G	BCR119
BC857W	BCM856BS	BCP56-16	BCR119S
BC858A	BCM856DS	BCP56-16T1	BCR119W
BC858B	BCM857BS	BCP56-16T1G	BCR129
BC858W	BCM857BV	BCP56-16T3G	BCR129W
BC859A	BCM857DS	BCP56T1	BCR133
BC859B	BCP49	BCP56T1G	BCR133S
BC859BW	BCP51	BCP56T3G	BCR133W
BC859C	BCP51-10	BCP68	BCR135
BC859CW	BCP51-16	BCP68-25	BCR135S
BC860A	BCP52	BCP68T1G	BCR135W
BC860B	BCP52-10	BCP69	BCR141
BC860BW	BCP52-16	BCP69-16	BCR141S
BC860C	BCP53	BCP69-25	BCR141W
BC860CW	BCP53-10	BCP69T1G	BCR142

Multisim 14.0 Full Components

BCR142W	BCR198	BCV49	BCW61C
BCR146	BCR198S	BCV61	BCW61D
BCR148	BCR198W	BCV61A	BCW65A
BCR148S	BCR22PN	BCV61B	BCW66F
BCR148W	BCR35PN	BCV61C	BCW67A
BCR158	BCR48PN	BCV62	BCW68F
BCR158W	BCR503	BCV62A	BCW69
BCR162	BCR505	BCV62B	BCW70
BCR166	BCR512	BCV62C	BCW71
BCR166W	BCR521	BCV63	BCW72
BCR169	BCR523	BCV63B	BCW89
BCR169S	BCR523U	BCV64B	BCX17
BCR169W	BCR533	BCV65	BCX17LT1G
BCR183	BCR553	BCV71	BCX18
BCR183S	BCR555	BCV72	BCX19
BCR183W	BCR562	BCW29	BCX38B
BCR185	BCR573	BCW30	BCX41
BCR185S	BCR583	BCW31	BCX42
BCR185W	BCV26	BCW32	BCX51
BCR191	BCV27	BCW33	BCX51-10
BCR191W	BCV28	BCW60B	BCX51-16
BCR192	BCV29	BCW60C	BCX52
BCR192W	BCV46	BCW60D	BCX52-10
BCR196	BCV47	BCW61A	BCX52-16
BCR196W	BCV48	BCW61B	BCX53

Multisim 14.0 Full Components

BCX53-10	BD138	BD675AG	BDV65BG
BCX53-16	BD138G	BD675G	BDW42G
BCX54	BD139	BD676AG	BDW46G
BCX54-10	BD139G	BD676G	BDW47G
BCX54-16	BD140	BD677AG	BDX33BG
BCX55	BD140G	BD677G	BDX33CG
BCX55-10	BD159G	BD678AG	BDX34BG
BCX55-16	BD179G	BD678G	BDX34CG
BCX56	BD180G	BD679AG	BDX53BG
BCX56-10	BD234G	BD679G	BDX53CG
BCX56-16	BD237G	BD680AG	BDX54BG
BCX70G	BD241CG	BD680G	BDX54CG
BCX70H	BD242BG	BD681G	BF245A
BCX70J	BD242CG	BD682G	BF245B
BCX70K	BD243CG	BD787G	BF245C
BCX71G	BD244BG	BD788G	BF246A
BCX71H	BD244CG	BD809G	BF247A
BCX71J	BD436TG	BD810G	BF256A
BCX71K	BD437G	BDP947	BF256B
BD135	BD437TG	BDP948	BF410A
BD135G	BD438G	BDP949	BF410B
BD136	BD439G	BDP950	BF410C
BD136G	BD440G	BDP953	BF410D
BD137	BD441G	BDP954	BF422G
BD137G	BD442G	BDV64BG	BF510

Multisim 14.0 Full Components

BF511	BF824W	BFN27	BICOLOR_LED_Red-Orange/Green
BF512	BF840	BFN39	
BF513	BF851A	BFP194	BIPOLAR_CURRENT
BF517	BF851B	BFQ31	BIPOLAR_VOLTAGE
BF545A	BF851C	BFR194	BJT_LPNP
BF545B	BF861A	BFR30	BJT_NPN
BF545C	BF861B	BFR31	BJT_NPN_4T
BF550	BF861C	BFS17	BJT_NPN_RATED
BF556A	BF904	BFS17H	BJT_PNP
BF556B	BF904R	BFS17P	BJT_PNP_4T
BF570	BF904WR	BFS19	BJT_PNP_RATED
BF620	BF908WR	BFS20	BOOST_CONVERTER
BF621	BF909	BFS20W	BOSCH-EDC16-BDM-HDR
BF622	BF909R	BFS60	
BF623	BF909WR	BFT46	BPASS
BF720	BF998	BFU308	BPV10NF
BF722	BF998R	BFU309	BPV22NF
BF723	BF998WR	BFU310	BPV23F
BF799	BFG135A	BFW10	BPV23NF
BF820	BFG193	BFW11	BPW 34
BF820W	BFG194	BFW12	BPW 34 FA
BF821	BFN18	BFW13	BPW 34 FAS
BF822	BFN19	BFW61	BPW 34 FASR
BF823	BFN24	BICOLOR_LED_Red/Green	BRUSHLESS_DC_MACHINE
BF824	BFN26		

Multisim 14.0 Full Components

BS170	BSC014N06NS	BSC030N03MS G	BSC059N04LS G
BSB008NE2LX	BSC014NE2LSI	BSC030N04NS G	BSC060N10NS3 G
BSB012N03LX3 G	BSC016N03LS G	BSC030P03NS3 G	BSC060P03NS3E G
BSB012NE2LX	BSC016N03MS G	BSC031N06NS3 G	BSC066N06NS
BSB012NE2LXI	BSC016N04LS G	BSC032N04LS	BSC067N06LS3 G
BSB013NE2LXI	BSC016N06NS	BSC032NE2LS	BSC070N10NS3 G
BSB014N04LX3 G	BSC017N04NS G	BSC034N06NS	BSC072N03LD G
BSB015N04NX3 G	BSC018N04LS G	BSC035N04LS G	BSC076N06NS3 G
BSB017N03LX3 G	BSC018NE2LS	BSC036NE7NS3 G	BSC077N12NS3 G
BSB028N06NN3 G	BSC018NE2LSI	BSC039N06NS	BSC079N10NS G
BSB044N08NN3 G	BSC019N02KS G	BSC042N03LS G	BSC080N03LS G
BSB056N10NN3 G	BSC019N04LS	BSC042N03MS G	BSC080N03MS G
BSB165N15NZ3 G	BSC019N04NS G	BSC042NE7NS3 G	BSC080P03LS G
BSB280N15NZ3 G	BSC020N03LS G	BSC046N02KS G	BSC082N10LS G
BSC009NE2LS	BSC020N03MS G	BSC046N10NS3 G	BSC084P03NS3 G
BSC010N04LS	BSC022N04LS	BSC047N08NS3 G	BSC084P03NS3E G
BSC010N04LSI	BSC024NE2LS	BSC050N03LS G	BSC0901NS
BSC010NE2LS	BSC025N03LS G	BSC050N03MS G	BSC0901NSI
BSC010NE2LSI	BSC025N03MS G	BSC050N04LS G	BSC0902NS
BSC011N03LS	BSC026N02KS G	BSC050NE2LS	BSC0902NSI
BSC011N03LSI	BSC026N04LS	BSC052N03LS	BSC0904NSI
BSC014N03LS G	BSC027N04LS G	BSC054N04NS G	BSC0906NS
BSC014N03MS G	BSC028N06LS3 G	BSC057N03LS G	BSC0908NS
BSC014N04LS	BSC028N06NS	BSC057N03MS G	BSC0909NS
BSC014N04LSI	BSC030N03LS G	BSC057N08NS3 G	BSC090N03LS G

Multisim 14.0 Full Components

BSC090N03MS G	BSC159N10LSF G	BSD235N	BSJ110
BSC0910NDI	BSC160N10NS3 G	BSD314SPE	BSL202SN
BSC0911ND	BSC16DN25NS3 G	BSD316SN	BSL205N
BSC0921NDI	BSC190N12NS3 G	BSD816SN	BSL207N
BSC0923NDI	BSC190N15NS3 G	BSD840N	BSL207SP
BSC0924NDI	BSC196N10NS G	BSE-080-01-L-D-A	BSL211SP
BSC0925ND	BSC200P03LS G	BSF024N03LT3 G	BSL214N
BSC093N04LS G	BSC205N10LS G	BSF030NE2LQ	BSL302SN
BSC097N06NS	BSC22DN20NS3 G	BSF035NE2LQ	BSL306N
BSC100N03LS G	BSC240N12NS3 G	BSF050N03LQ3 G	BSL307SP
BSC100N03MS G	BSC252N10NSF G	BSF134N10NJ3 G	BSL308PE
BSC100N06LS3 G	BSC265N10LSF G	BSF450NE7NH3 G	BSL314PE
BSC100N10NSF G	BSC320N20NS3 G	BSH103	BSL606SN
BSC105N10LSF G	BSC340N08NS3 G	BSH105	BSL802SN
BSC109N10NS3 G	BSC360N15NS3 G	BSH108	BSL806N
BSC110N06NS3 G	BSC440N10NS3 G	BSH111	BSN011NE2LS
BSC118N10NS G	BSC500N20NS3 G	BSH114	BSN011NE2LSI
BSC120N03LS G	BSC520N15NS3 G	BSH121	BSN012N03LS
BSC120N03MS G	BSC600N25NS3 G	BSH201	BSN012N03LSI
BSC123N08NS3 G	BSC750N10ND G	BSH202	BSN045NE2LS
BSC123N10LS G	BSC900N20NS3 G	BSH203	BSN048N03LS
BSC12DN20NS3 G	BSD214	BSH205	BSN20
BSC130P03LS G	BSD214SN	BSH207	BSO033N03MS G
BSC150N03LD G	BSD215	BSJ108	BSO040N03MS G
BSC152N10NSF G	BSD223P	BSJ109	BSO051N03MS G

Multisim 14.0 Full Components

BSO065N03MS G	BSP123	BSP315P	BSR302N
BSO080P03NS3 G	BSP125	BSP316P	BSR31
BSO080P03NS3E G	BSP126	BSP317P	BSR315P
BSO080P03S H	BSP129	BSP32	BSR316P
BSO083N03MS G	BSP130	BSP324	BSR33
BSO110N03MS G	BSP135	BSP33	BSR41
BSO130N03MS G	BSP149	BSP41	BSR43
BSO130P03S H	BSP16T1G	BSP43	BSR56
BSO150N03MD G	BSP170P	BSP50	BSR57
BSO200P03S H	BSP171P	BSP51	BSR58
BSO201SP H	BSP19	BSP52	BSR606N
BSO203SP H	BSP19AT1G	BSP52T1G	BSR802N
BSO207P H	BSP204	BSP52T3G	BSR92P
BSO211P H	BSP204A	BSP60	BSS110
BSO220N03MD G	BSP205	BSP61	BSS123
BSO220N03MS G	BSP206	BSP613P	BSS123LT1G
BSO301SP H	BSP220	BSP62	BSS126
BSO303SP H	BSP225	BSP88	BSS127
BSO330N02K G	BSP230	BSP89	BSS131
BSO613SPV G	BSP250	BSP92P	BSS138BK
BSP 60 E6327	BSP296	BSR14	BSS138BKS
BSP030	BSP297	BSR16	BSS138BKW
BSP100	BSP304	BSR19A	BSS138LT1G
BSP110	BSP304A	BSR202N	BSS138LT3G
BSP122	BSP31	BSR30	BSS138N

Multisim 14.0 Full Components

BSS138P	BSS806N	BST52	BSZ058N03LS G
BSS138PS	BSS816NW	BST60	BSZ058N03MS G
BSS138PW	BSS83	BST61	BSZ060NE2LS
BSS138W	BSS83P	BST62	BSZ065N03LS
BSS139	BSS84	BST82	BSZ067N06LS3 G
BSS159N	BSS84AK	BSV236SP	BSZ068N06NS
BSS169	BSS84AKM	BSV52	BSZ076N06NS3 G
BSS192	BSS84AKMB	BSV78	BSZ086P03NS3 G
BSS192P	BSS84AKS	BSV79	BSZ086P03NS3E G
BSS205N	BSS84AKT	BSV80	BSZ088N03LS G
BSS209PW	BSS84AKV	BSV81	BSZ088N03MS G
BSS214N	BSS84AKW	BSZ018NE2LS	BSZ0901NS
BSS214NW	BSS84LT1G	BSZ018NE2LSI	BSZ0901NSI
BSS223PW	BSS84P	BSZ019N03LS	BSZ0902NS
BSS225	BSS84PW	BSZ023N04LS	BSZ0902NSI
BSS306N	BSS84PW H6327	BSZ028N04LS	BSZ0904NSI
BSS308PE	BSS87	BSZ034N04LS	BSZ0907ND
BSS314PE	BSS92	BSZ035N03LS G	BSZ0908ND
BSS315P	BST100	BSZ035N03MS G	BSZ0909NS
BSS316N	BST110	BSZ036NE2LS	BSZ097N04LS G
BSS606N	BST120	BSZ040N04LS G	BSZ100N03LS G
BSS63	BST122	BSZ042N04NS G	BSZ100N03MS G
BSS64	BST39	BSZ042N06NS	BSZ100N06LS3 G
BSS670S2L	BST50	BSZ050N03LS G	BSZ100N06NS
BSS7728N	BST51	BSZ050N03MS G	BSZ105N04NS G

Multisim 14.0 Full Components

BSZ110N06NS3 G	BT134W	BT169_B	BUF602IDBVR
BSZ120P03NS3 G	BT136	BTA140	BUFFER
BSZ120P03NS3E G	BT136-E	BTW38_600R	BUH100G
BSZ123N08NS3 G	BT136-F	BTW40_400R	BUH150G
BSZ12DN20NS3 G	BT136-G	BTW42_600R	BUH50G
BSZ130N03LS G	BT137	BTW43	BUK6207-55C
BSZ130N03MS G	BT137-E	BTW45_400R	BUK6209-30C
BSZ150N10LS3 G	BT137-F	BTY79_400R	BUK6210-55C
BSZ160N10NS3 G	BT137-G	BTY91_400R	BUK6211-75C
BSZ165N04NS G	BT138	BU323ZG	BUK6212-40C
BSZ16DN25NS3 G	BT138-E	BU406G	BUK6213-30C
BSZ180P03NS3 G	BT138-F	BUB323ZG	BUK6215-75C
BSZ180P03NS3E G	BT138-G	BUB323ZT4G	BUK6217-55C
BSZ22DN20NS3 G	BT139	BUCK_BOOST_CONVERTER	BUK6218-40C
BSZ240N12NS3 G	BT139-E	BUCK_CONVERTER	BUK6226-75C
BSZ340N08NS3 G	BT139-F	BUD42D-1G	BUK6228-55C
BSZ42DN25NS3 G	BT139-G	BUD42DT4G	BUK6246-75C
BSZ440N10NS3 G	BT145_500R	BUF	BUK624R5-30C
BSZ520N15NS3 G	BT148_400R	BUF_3S_AHOE	BUK625R0-40C
BSZ900N15NS3 G	BT148W_400R	BUF_3S_ALOE	BUK625R2-30C
BSZ900N20NS3 G	BT149_B	BUF_CO	BUK626R2-40C
BT134	BT150_500R	BUF_INV	BUK6507-55C
BT134-E	BT151_500R	BUF601AP	BUK6507-75C
BT134-F	BT152_400R	BUF602ID	BUK6510-75C
BT134-G	BT153_500R		BUK652R1-30C

Multisim 14.0 Full Components

BUK652R6-40C	BUK7514-60E	BUK7E1R6-30E	BUK7Y15-100E
BUK653R3-30C	BUK751R6-30E	BUK7E1R8-40E	BUK7Y153-100E
BUK653R4-40C	BUK751R8-40E	BUK7E1R9-40E	BUK7Y15-60E
BUK653R5-55C	BUK752R3-40E	BUK7E2R3-40E	BUK7Y18-55B
BUK653R7-30C	BUK752R7-60E	BUK7E2R6-60E	BUK7Y18-75B
BUK654R0-75C	BUK753R1-40E	BUK7E3R1-40E	BUK7Y20-30B
BUK654R6-55C	BUK753R5-60E	BUK7E3R5-60E	BUK7Y21-40E
BUK654R8-40C	BUK753R8-80E	BUK7E4R0-80E	BUK7Y22-100E
BUK655R0-75C	BUK754R0-40C	BUK7E4R6-60E	BUK7Y25-40B
BUK6607-55C	BUK754R7-60E	BUK7E5R2-100E	BUK7Y25-60E
BUK6607-75C	BUK755R4-100E	BUK7E8R3-40E	BUK7Y25-80E
BUK6610-75C	BUK758R3-40E	BUK7K25-40E	BUK7Y28-75B
BUK661R8-30C	BUK7613-100E	BUK7K5R1-30E	BUK7Y29-40E
BUK661R9-40C	BUK761R3-30E	BUK7K5R6-30E	BUK7Y35-55B
BUK662R4-40C	BUK761R4-30E	BUK7K6R8-40E	BUK7Y38-100E
BUK662R5-30C	BUK761R5-40E	BUK7Y07-30B	BUK7Y41-80E
BUK662R7-55C	BUK761R6-40E	BUK7Y08-40B	BUK7Y43-60E
BUK663R2-40C	BUK762R4-60E	BUK7Y102-100B	BUK7Y4R4-40E
BUK663R5-30C	BUK7631-100E	BUK7Y10-30B	BUK7Y4R8-60E
BUK663R5-55C	BUK763R8-80E	BUK7Y113-100E	BUK7Y53-100B
BUK663R7-75C	BUK764R2-80E	BUK7Y12-100E	BUK7Y54-75B
BUK664R4-55C	BUK765R0-100E	BUK7Y12-40E	BUK7Y59-60E
BUK664R6-40C	BUK768R1-100E	BUK7Y12-55B	BUK7Y65-100E
BUK6C2R1-55C	BUK769R6-80E	BUK7Y13-40B	BUK7Y6R0-60E
BUK6C3R3-75C	BUK7E13-60E	BUK7Y14-80E	BUK7Y72-80E

Multisim 14.0 Full Components

BUK7Y7R6-40E	BUK9E15-60E	BUK9Y12-55B	BUK9Y59-60E
BUK7Y7R8-80E	BUK9E1R6-30E	BUK9Y14-40B	BUK9Y65-100E
BUK7Y8R7-60E	BUK9E2R3-40E	BUK9Y14-80E	BUK9Y6R0-60E
BUK7Y98-80E	BUK9E2R8-60E	BUK9Y15-100E	BUK9Y72-80E
BUK7Y9R9-80E	BUK9E3R7-60E	BUK9Y153-100E	BUK9Y7R6-40E
BUK9515-60E	BUK9E4R4-80E	BUK9Y15-60E	BUK9Y8R5-80E
BUK951R6-30E	BUK9E4R9-60E	BUK9Y19-55B	BUK9Y8R7-60E
BUK951R9-40E	BUK9E6R1-100E	BUK9Y19-75B	BUL45D2G
BUK952R3-40E	BUK9E8R5-40E	BUK9Y21-40E	BUL45G
BUK952R8-60E	BUK9K18-40E	BUK9Y22-100E	BUV21G
BUK953R2-40E	BUK9K29-100E	BUK9Y22-30B	BUV22G
BUK953R5-60E	BUK9K35-60E	BUK9Y25-60E	BUV26G
BUK954R4-80E	BUK9K45-100E	BUK9Y25-80E	BUX85G
BUK958R5-40E	BUK9K52-60E	BUK9Y27-40B	BUZZER
BUK9611-80E	BUK9K6R2-40E	BUK9Y29-40E	BVSS123LT1G
BUK9615-100E	BUK9K89-100E	BUK9Y30-75B	BVSS138LT1G
BUK961R4-30E	BUK9Y07-30B	BUK9Y38-100E	BY228
BUK961R5-30E	BUK9Y09-40B	BUK9Y3R0-40E	BY328
BUK961R6-40E	BUK9Y104-100B	BUK9Y40-55B	BY438
BUK962R5-60E	BUK9Y107-80E	BUK9Y41-80E	BY448
BUK9637-100E	BUK9Y11-30B	BUK9Y43-60E	BY458
BUK964R2-80E	BUK9Y113-100E	BUK9Y4R4-40E	BY505
BUK964R7-80E	BUK9Y11-80E	BUK9Y4R8-60E	BY527
BUK965R8-100E	BUK9Y12-100E	BUK9Y53-100B	BY584
BUK969R3-100E	BUK9Y12-40E	BUK9Y58-75B	BY627

Multisim 14.0 Full Components

BY705	BYD13K	BYD37D	BYD77G
BY706	BYD13M	BYD37G	BYG10G-E3/TR
BY710	BYD14D	BYD37J	BYG10J-E3/TR
BY711	BYD14G	BYD37K	BYG20J-E3/TR
BY712	BYD14J	BYD37M	BYG21M-E3/TR
BY713	BYD14K	BYD73A	BYG22D-E3/TR
BY714	BYD14M	BYD73B	BYG24J-E3/TR3
BY715	BYD17D	BYD73C	BYM10-100
BY716	BYD17G	BYD73D	BYM10-1000
BY717	BYD17J	BYD73E	BYM10-1000-E3/97
BY718	BYD17K	BYD73F	BYM10-200
BY719	BYD17M	BYD73G	BYM10-400
BY720	BYD31D	BYD74A	BYM10-50
BY721	BYD31G	BYD74B	BYM10-600
BY722	BYD31J	BYD74C	BYM10-800
BY723	BYD33D	BYD74D	BYM11-100
BYD11	BYD33G	BYD74E	BYM11-1000
BYD11D	BYD33J	BYD74F	BYM11-1000-E3/96
BYD11G	BYD33K	BYD74G	BYM11-100-E3/96
BYD11J	BYD33M	BYD77A	BYM11-200
BYD11K	BYD34D	BYD77B	BYM11-400
BYD11M	BYD34G	BYD77C	BYM11-50
BYD13D	BYD34J	BYD77D	BYM11-600
BYD13G	BYD34K	BYD77E	BYM11-800
BYD13J	BYD34M	BYD77F	BYM12-400-E3/96

Multisim 14.0 Full Components

BYM26A	BYV26E	BYW95B	BZA968A
BYM26B	BYV27-100	BYW95C	BZA968AVL
BYM26C	BYV27-50	BYW96D	BZB100A
BYM26D	BYV28-100	BYW96E	BZB784-C10
BYM26E	BYV28-150	BYX10G	BZB784-C11
BYM36A	BYV28-200	BYX110GP	BZB784-C12
BYM36B	BYV28-50	BZA408B	BZB784-C13
BYM36C	BYV32-200G	BZA418A	BZB784-C15
BYM36D	BYV36A	BZA420A	BZB784-C2V4
BYM36E	BYV36B	BZA456A	BZB784-C2V7
BYM56A	BYV36C	BZA462A	BZB784-C3V0
BYM56B	BYV36D	BZA820A	BZB784-C3V3
BYM56C	BYV36E	BZA856A	BZB784-C3V6
BYM56D	BYV95A	BZA856AL	BZB784-C3V9
BYM56E	BYV95B	BZA856AVL	BZB784-C4V3
BYS10-45-E3/TR	BYV95C	BZA862A	BZB784-C4V7
BYS11-90-E3/TR	BYV96D	BZA862AL	BZB784-C5V1
BYT28-300-E3/45	BYV96E	BZA862AVL	BZB784-C5V6
BYV10-20	BYW29-200G	BZA868A	BZB784-C6V2
BYV10-30	BYW51-200G	BZA868AL	BZB784-C6V8
BYV10-40	BYW54	BZA868AVL	BZB784-C7V5
BYV26A	BYW55	BZA956A	BZB784-C8V2
BYV26B	BYW56	BZA956AVL	BZB784-C9V1
BYV26C	BYW80-200G	BZA962A	BZB84-B10
BYV26D	BYW95A	BZA962AVL	BZB84-B11

Multisim 14.0 Full Components

BZB84-B12	BZB84-B5V1	BZB84-C36	BZB984-C13
BZB84-B13	BZB84-B5V6	BZB84-C39	BZB984-C15
BZB84-B15	BZB84-B62	BZB84-C3V0	BZB984-C2V4
BZB84-B16	BZB84-B68	BZB84-C3V3	BZB984-C2V7
BZB84-B18	BZB84-B6V2	BZB84-C3V6	BZB984-C3V0
BZB84-B20	BZB84-B6V8	BZB84-C3V9	BZB984-C3V3
BZB84-B22	BZB84-B75	BZB84-C43	BZB984-C3V6
BZB84-B24	BZB84-B7V5	BZB84-C47	BZB984-C3V9
BZB84-B27	BZB84-B8V2	BZB84-C4V3	BZB984-C4V3
BZB84-B2V4	BZB84-B9V1	BZB84-C4V7	BZB984-C4V7
BZB84-B2V7	BZB84-C10	BZB84-C51	BZB984-C5V1
BZB84-B30	BZB84-C11	BZB84-C56	BZB984-C5V6
BZB84-B33	BZB84-C12	BZB84-C5V1	BZB984-C6V2
BZB84-B36	BZB84-C13	BZB84-C5V6	BZB984-C6V8
BZB84-B39	BZB84-C15	BZB84-C62	BZB984-C7V5
BZB84-B3V0	BZB84-C16	BZB84-C68	BZB984-C8V2
BZB84-B3V3	BZB84-C18	BZB84-C6V2	BZB984-C9V1
BZB84-B3V6	BZB84-C20	BZB84-C6V8	BZT52H-B10
BZB84-B3V9	BZB84-C22	BZB84-C75	BZT52H-B11
BZB84-B43	BZB84-C24	BZB84-C7V5	BZT52H-B12
BZB84-B47	BZB84-C27	BZB84-C8V2	BZT52H-B13
BZB84-B4V3	BZB84-C2V4	BZB84-C9V1	BZT52H-B15
BZB84-B4V7	BZB84-C2V7	BZB984-C10	BZT52H-B16
BZB84-B51	BZB84-C30	BZB984-C11	BZT52H-B18
BZB84-B56	BZB84-C33	BZB984-C12	BZT52H-B20

Multisim 14.0 Full Components

BZT52H-B22	BZT52H-C11	BZT52H-C5V1	BZV55-B2V7
BZT52H-B24	BZT52H-C12	BZT52H-C5V6	BZV55-B30
BZT52H-B27	BZT52H-C13	BZT52H-C62	BZV55-B33
BZT52H-B2V4	BZT52H-C15	BZT52H-C68	BZV55-B36
BZT52H-B2V7	BZT52H-C16	BZT52H-C6V2	BZV55-B39
BZT52H-B30	BZT52H-C18	BZT52H-C6V8	BZV55-B3V0
BZT52H-B33	BZT52H-C20	BZT52H-C75	BZV55-B3V3
BZT52H-B36	BZT52H-C22	BZT52H-C7V5	BZV55-B3V6
BZT52H-B39	BZT52H-C24	BZT52H-C8V2	BZV55-B3V9
BZT52H-B3V0	BZT52H-C27	BZT52H-C9V1	BZV55-B43
BZT52H-B43	BZT52H-C2V4	BZV49-C12	BZV55-B47
BZT52H-B47	BZT52H-C2V7	BZV49-C16	BZV55-B4V3
BZT52H-B51	BZT52H-C30	BZV49-C3V6	BZV55-B4V7
BZT52H-B56	BZT52H-C33	BZV55-B10	BZV55-B51
BZT52H-B5V1	BZT52H-C36	BZV55-B11	BZV55-B56
BZT52H-B5V6	BZT52H-C39	BZV55-B12	BZV55-B5V1
BZT52H-B62	BZT52H-C3V0	BZV55-B13	BZV55-B5V6
BZT52H-B68	BZT52H-C3V6	BZV55-B15	BZV55-B68
BZT52H-B6V2	BZT52H-C3V9	BZV55-B16	BZV55-B6V2
BZT52H-B6V8	BZT52H-C43	BZV55-B18	BZV55-B6V8
BZT52H-B75	BZT52H-C47	BZV55-B20	BZV55-B75
BZT52H-B7V5	BZT52H-C4V3	BZV55-B22	BZV55-B7V5
BZT52H-B8V2	BZT52H-C4V7	BZV55-B24	BZV55-B8V2
BZT52H-B9V1	BZT52H-C51	BZV55-B27	BZV55-B9V1
BZT52H-C10	BZT52H-C56	BZV55-B2V4	BZV55-C10

Multisim 14.0 Full Components

BZV55-C11	BZV55-F2V4	BZV60-B4V7	BZV60-C2V7
BZV55-C12	BZV60-B10	BZV60-B51	BZV60-C30
BZV55-C13	BZV60-B11	BZV60-B56	BZV60-C33
BZV55-C15	BZV60-B12	BZV60-B5V1	BZV60-C36
BZV55-C16	BZV60-B13	BZV60-B5V6	BZV60-C39
BZV55-C18	BZV60-B15	BZV60-B62	BZV60-C3V0
BZV55-C27	BZV60-B16	BZV60-B68	BZV60-C3V3
BZV55-C2V4	BZV60-B18	BZV60-B6V2	BZV60-C3V6
BZV55-C2V7	BZV60-B20	BZV60-B6V8	BZV60-C3V9
BZV55-C33	BZV60-B22	BZV60-B75	BZV60-C43
BZV55-C3V0	BZV60-B24	BZV60-B7V5	BZV60-C47
BZV55-C3V3	BZV60-B27	BZV60-B8V2	BZV60-C4V3
BZV55-C3V6	BZV60-B2V4	BZV60-B9V1	BZV60-C4V7
BZV55-C3V9	BZV60-B2V7	BZV60-C10	BZV60-C51
BZV55-C43	BZV60-B30	BZV60-C11	BZV60-C56
BZV55-C47	BZV60-B33	BZV60-C12	BZV60-C5V1
BZV55-C4V3	BZV60-B36	BZV60-C13	BZV60-C5V6
BZV55-C4V7	BZV60-B39	BZV60-C15	BZV60-C62
BZV55-C5V1	BZV60-B3V0	BZV60-C16	BZV60-C68
BZV55-C5V6	BZV60-B3V3	BZV60-C18	BZV60-C6V2
BZV55-C6V2	BZV60-B3V6	BZV60-C20	BZV60-C6V8
BZV55-C6V8	BZV60-B3V9	BZV60-C22	BZV60-C75
BZV55-C7V5	BZV60-B43	BZV60-C24	BZV60-C7V5
BZV55-C8V2	BZV60-B47	BZV60-C27	BZV60-C8V2
BZV55-C9V1	BZV60-B4V3	BZV60-C2V4	BZV60-C9V1

Multisim 14.0 Full Components

BZV80	BZV85-C62	BZV90-C33	BZW03-C11
BZV85-C10	BZV85-C68	BZV90-C36	BZW03-C110
BZV85-C11	BZV85-C6V2	BZV90-C39	BZW03-C12
BZV85-C12	BZV85-C6V8	BZV90-C3V0	BZW03-C120
BZV85-C13	BZV85-C75	BZV90-C3V3	BZW03-C13
BZV85-C15	BZV85-C7V5	BZV90-C3V6	BZW03-C130
BZV85-C16	BZV85-C8V2	BZV90-C3V9	BZW03-C15
BZV85-C18	BZV86-1V4	BZV90-C43	BZW03-C150
BZV85-C20	BZV86-2V0	BZV90-C47	BZW03-C16
BZV85-C22	BZV86-2V6	BZV90-C4V3	BZW03-C160
BZV85-C24	BZV86-3V2	BZV90-C4V7	BZW03-C18
BZV85-C27	BZV90-C10	BZV90-C51	BZW03-C180
BZV85-C30	BZV90-C11	BZV90-C56	BZW03-C20
BZV85-C33	BZV90-C12	BZV90-C5V1	BZW03-C200
BZV85-C36	BZV90-C13	BZV90-C5V6	BZW03-C22
BZV85-C39	BZV90-C15	BZV90-C62	BZW03-C220
BZV85-C3V6	BZV90-C16	BZV90-C68	BZW03-C24
BZV85-C3V9	BZV90-C18	BZV90-C6V2	BZW03-C240
BZV85-C43	BZV90-C20	BZV90-C6V8	BZW03-C27
BZV85-C47	BZV90-C22	BZV90-C75	BZW03-C270
BZV85-C4V3	BZV90-C24	BZV90-C7V5	BZW03-C30
BZV85-C4V7	BZV90-C27	BZV90-C8V2	BZW03-C33
BZV85-C51	BZV90-C2V4	BZV90-C9V1	BZW03-C36
BZV85-C5V1	BZV90-C2V7	BZW03-C10	BZW03-C39
BZV85-C5V6	BZV90-C30	BZW03-C100	BZW03-C43

Multisim 14.0 Full Components

BZW03-C47	BZX384-B30	BZX384-C11	BZX384-C68
BZW03-C51	BZX384-B33	BZX384-C12	BZX384-C6V2
BZW03-C56	BZX384-B36	BZX384-C13	BZX384-C6V8
BZW03-C62	BZX384-B39	BZX384-C16	BZX384-C75
BZW03-C68	BZX384-B3V0	BZX384-C20	BZX384-C7V5
BZW03-C75	BZX384-B3V3	BZX384-C22	BZX384-C8V2
BZW03-C7V5	BZX384-B3V6	BZX384-C24	BZX384-C9V1
BZW03-C82	BZX384-B3V9	BZX384-C2V4	BZX55C10
BZW03-C8V2	BZX384-B43	BZX384-C2V7	BZX55C11
BZW03-C91	BZX384-B47	BZX384-C30	BZX55C12
BZW03-C9V1	BZX384-B4V3	BZX384-C33	BZX55C13
BZX100A	BZX384-B4V7	BZX384-C36	BZX55C15
BZX384-B10	BZX384-B51	BZX384-C39	BZX55C16
BZX384-B11	BZX384-B56	BZX384-C3V0	BZX55C18
BZX384-B12	BZX384-B5V1	BZX384-C3V3	BZX55C20
BZX384-B13	BZX384-B5V6	BZX384-C3V6	BZX55C22
BZX384-B15	BZX384-B62	BZX384-C3V9	BZX55C24
BZX384-B16	BZX384-B68	BZX384-C43	BZX55C27
BZX384-B18	BZX384-B6V2	BZX384-C47	BZX55C2V4
BZX384-B20	BZX384-B6V8	BZX384-C4V3	BZX55C2V7
BZX384-B22	BZX384-B75	BZX384-C4V7	BZX55C30
BZX384-B24	BZX384-B7V5	BZX384-C51	BZX55C33
BZX384-B27	BZX384-B8V2	BZX384-C56	BZX55C36
BZX384-B2V4	BZX384-B9V1	BZX384-C5V1	BZX55C39
BZX384-B2V7	BZX384-C10	BZX384-C62	BZX55C3V0

Multisim 14.0 Full Components

BZX55C3V3	BZX585-B15	BZX585-B62	BZX585-C3V9
BZX55C3V6	BZX585-B16	BZX585-B68	BZX585-C43
BZX55C3V9	BZX585-B18	BZX585-B6V2	BZX585-C47
BZX55C43	BZX585-B20	BZX585-B6V8	BZX585-C4V3
BZX55C47	BZX585-B22	BZX585-B75	BZX585-C4V7
BZX55C4V3	BZX585-B24	BZX585-B7V5	BZX585-C51
BZX55C4V7	BZX585-B27	BZX585-B8V2	BZX585-C56
BZX55C51	BZX585-B2V4	BZX585-B9V1	BZX585-C5V1
BZX55C56	BZX585-B2V7	BZX585-C10	BZX585-C62
BZX55C5V1	BZX585-B30	BZX585-C11	BZX585-C68
BZX55C5V6	BZX585-B33	BZX585-C12	BZX585-C6V2
BZX55C62	BZX585-B36	BZX585-C13	BZX585-C6V8
BZX55C68	BZX585-B39	BZX585-C16	BZX585-C75
BZX55C6V2	BZX585-B3V0	BZX585-C20	BZX585-C7V5
BZX55C6V8	BZX585-B3V3	BZX585-C22	BZX585-C8V2
BZX55C75	BZX585-B3V6	BZX585-C24	BZX585-C9V1
BZX55C7V5	BZX585-B3V9	BZX585-C2V4	BZX79-A10
BZX55C82	BZX585-B43	BZX585-C2V7	BZX79-A11
BZX55C8V2	BZX585-B47	BZX585-C30	BZX79-A12
BZX55C91	BZX585-B4V3	BZX585-C33	BZX79-A13
BZX55C9V1	BZX585-B4V7	BZX585-C36	BZX79-A15
BZX585-B10	BZX585-B51	BZX585-C39	BZX79-A16
BZX585-B11	BZX585-B56	BZX585-C3V0	BZX79-A18
BZX585-B12	BZX585-B5V1	BZX585-C3V3	BZX79-A20
BZX585-B13	BZX585-B5V6	BZX585-C3V6	BZX79-A22

Multisim 14.0 Full Components

BZX79-A24	BZX79-A7V5	BZX79-B4V3	BZX79-C18
BZX79-A27	BZX79-A8V2	BZX79-B4V7	BZX79-C180
BZX79-A2V4	BZX79-A9V1	BZX79-B51	BZX79-C20
BZX79-A2V7	BZX79-B10	BZX79-B56	BZX79-C200
BZX79-A30	BZX79-B11	BZX79-B5V1	BZX79-C22
BZX79-A33	BZX79-B12	BZX79-B62	BZX79-C24
BZX79-A36	BZX79-B13	BZX79-B68	BZX79-C27
BZX79-A3V0	BZX79-B15	BZX79-B6V2	BZX79-C2V4
BZX79-A3V3	BZX79-B16	BZX79-B6V8	BZX79-C2V7
BZX79-A3V6	BZX79-B18	BZX79-B75	BZX79-C30
BZX79-A3V9	BZX79-B20	BZX79-B7V5	BZX79-C33
BZX79-A40	BZX79-B22	BZX79-B8V2	BZX79-C36
BZX79-A43	BZX79-B24	BZX79-B9V1	BZX79-C39
BZX79-A47	BZX79-B27	BZX79-C10	BZX79-C3V0
BZX79-A4V3	BZX79-B2V4	BZX79-C100	BZX79-C3V3
BZX79-A4V7	BZX79-B2V7	BZX79-C11	BZX79-C3V6
BZX79-A51	BZX79-B30	BZX79-C110	BZX79-C3V9
BZX79-A56	BZX79-B33	BZX79-C12	BZX79-C43
BZX79-A5V1	BZX79-B36	BZX79-C120	BZX79-C47
BZX79-A5V6	BZX79-B39	BZX79-C13	BZX79-C4V3
BZX79-A62	BZX79-B3V3	BZX79-C130	BZX79-C4V7
BZX79-A68	BZX79-B3V6	BZX79-C15	BZX79-C51
BZX79-A6V2	BZX79-B3V9	BZX79-C150	BZX79-C56
BZX79-A6V8	BZX79-B43	BZX79-C16	BZX79-C5V1
BZX79-A75	BZX79-B47	BZX79-C160	BZX79-C5V6

Multisim 14.0 Full Components

BZX79-C62	BZX83-C3V3	BZX84-A30	BZX84-B11
BZX79-C68	BZX83-C3V6	BZX84-A33	BZX84-B12
BZX79-C6V2	BZX83-C3V9	BZX84-A36	BZX84-B13
BZX79-C6V8	BZX83-C4V3	BZX84-A39	BZX84-B15
BZX79-C75	BZX83-C4V7	BZX84-A3V0	BZX84-B16
BZX79-C7V5	BZX83-C5V1	BZX84-A3V3	BZX84B16LT1G
BZX79-C82	BZX83-C5V6	BZX84-A3V6	BZX84-B18
BZX79-C8V2	BZX83-C6V2	BZX84-A3V9	BZX84-B20
BZX79-C91	BZX83-C6V8	BZX84-A43	BZX84-B22
BZX79-C9V1	BZX83-C7V5	BZX84-A47	BZX84-B24
BZX83-C10	BZX83-C8V2	BZX84-A4V3	BZX84-B27
BZX83-C11	BZX83-C9V1	BZX84-A4V7	BZX84-B2V4
BZX83-C12	BZX84-A10	BZX84-A51	BZX84-B2V7
BZX83-C13	BZX84-A11	BZX84-A56	BZX84-B30
BZX83-C15	BZX84-A12	BZX84-A5V1	BZX84-B33
BZX83-C16	BZX84-A13	BZX84-A5V6	BZX84-B36
BZX83-C18	BZX84-A15	BZX84-A62	BZX84-B39
BZX83-C20	BZX84-A16	BZX84-A68	BZX84-B3V0
BZX83-C22	BZX84-A18	BZX84-A6V2	BZX84-B3V3
BZX83-C24	BZX84-A20	BZX84-A6V8	BZX84-B3V6
BZX83-C27	BZX84-A22	BZX84-A75	BZX84-B3V9
BZX83-C2V7	BZX84-A24	BZX84-A7V5	BZX84-B43
BZX83-C30	BZX84-A27	BZX84-A8V2	BZX84-B47
BZX83-C33	BZX84-A2V4	BZX84-A9V1	BZX84-B4V3
BZX83-C3V0	BZX84-A2V7	BZX84-B10	BZX84-B4V7

Multisim 14.0 Full Components

BZX84B4V7LT1G	BZX84-C15	BZX84-C47	BZX84C7V5LT1G
BZX84-B51	BZX84C15LT1	BZX84-C4V3	BZX84-C8V2
BZX84-B56	BZX84C15LT1G	BZX84-C4V7	BZX84C8V2LT1G
BZX84-B5V1	BZX84C15LT3G	BZX84C4V7LT1G	BZX84-C9V1
BZX84B5V1LT1G	BZX84-C16	BZX84C4V7LT3G	BZX84C9V1LT1G
BZX84-B5V6	BZX84-C18	BZX84-C51	BZX84C9V1LT3G
BZX84B5V6LT1G	BZX84-C20	BZX84-C56	BZX84J-B10
BZX84-B62	BZX84-C22	BZX84-C5V1	BZX84J-B11
BZX84-B68	BZX84-C24	BZX84C5V1LT1G	BZX84J-B12
BZX84-B6V2	BZX84-C27	BZX84C5V1LT3G	BZX84J-B13
BZX84B6V2LT1G	BZX84-C2V4	BZX84-C5V6	BZX84J-B15
BZX84-B6V8	BZX84-C2V7	BZX84C5V6LT1G	BZX84J-B16
BZX84B6V8LT1G	BZX84-C30	BZX84C5V6LT3G	BZX84J-B18
BZX84-B75	BZX84-C33	BZX84-C62	BZX84J-B20
BZX84-B7V5	BZX84C33LT1G	BZX84-C68	BZX84J-B22
BZX84B7V5LT1G	BZX84C33LT3G	BZX84C68LT1G	BZX84J-B24
BZX84-B8V2	BZX84-C36	BZX84-C6V2	BZX84J-B27
BZX84B8V2LT1G	BZX84C36LT1G	BZX84C6V2LT1G	BZX84J-B2V4
BZX84-B9V1	BZX84-C39	BZX84C6V2LT3G	BZX84J-B2V7
BZX84B9V1LT1G	BZX84-C3V0	BZX84-C6V8	BZX84J-B30
BZX84-C10	BZX84C3V0LT1G	BZX84C6V8LT1G	BZX84J-B33
BZX84-C11	BZX84-C3V3	BZX84C6V8LT3G	BZX84J-B36
BZX84-C12	BZX84-C3V6	BZX84-C75	BZX84J-B39
BZX84C12LT1G	BZX84-C3V9	BZX84C75LT1G	BZX84J-B3V0
BZX84-C13	BZX84-C43	BZX84-C7V5	BZX84J-B3V3

Multisim 14.0 Full Components

BZX84J-B3V6	BZX84J-C20	BZX84J-C6V8	BZX85-C47
BZX84J-B3V9	BZX84J-C22	BZX84J-C75	BZX85-C4V3
BZX84J-B43	BZX84J-C24	BZX84J-C7V5	BZX85-C4V7
BZX84J-B47	BZX84J-C27	BZX84J-C8V2	BZX85-C51
BZX84J-B4V3	BZX84J-C2V4	BZX84J-C9V1	BZX85-C56
BZX84J-B4V7	BZX84J-C2V7	BZX85-C10	BZX85-C5V1
BZX84J-B51	BZX84J-C30	BZX85-C100	BZX85-C5V6
BZX84J-B56	BZX84J-C33	BZX85-C11	BZX85-C62
BZX84J-B5V1	BZX84J-C36	BZX85-C12	BZX85-C68
BZX84J-B5V6	BZX84J-C39	BZX85-C13	BZX85-C6V2
BZX84J-B62	BZX84J-C3V0	BZX85-C15	BZX85-C6V8
BZX84J-B68	BZX84J-C3V3	BZX85-C16	BZX85-C75
BZX84J-B6V2	BZX84J-C3V6	BZX85-C18	BZX85-C7V5
BZX84J-B6V8	BZX84J-C3V9	BZX85-C20	BZX85-C82
BZX84J-B75	BZX84J-C43	BZX85-C22	BZX85-C8V2
BZX84J-B7V5	BZX84J-C47	BZX85-C24	BZX85-C91
BZX84J-B8V2	BZX84J-C4V3	BZX85-C27	BZX85-C9V1
BZX84J-B9V1	BZX84J-C4V7	BZX85-C30	BZX884-B10
BZX84J-C10	BZX84J-C51	BZX85-C33	BZX884-B11
BZX84J-C11	BZX84J-C56	BZX85-C36	BZX884-B12
BZX84J-C12	BZX84J-C5V1	BZX85-C39	BZX884-B13
BZX84J-C13	BZX84J-C5V6	BZX85-C3V3	BZX884-B15
BZX84J-C15	BZX84J-C62	BZX85-C3V6	BZX884-B16
BZX84J-C16	BZX84J-C68	BZX85-C3V9	BZX884-B18
BZX84J-C18	BZX84J-C6V2	BZX85-C43	BZX884-B20

Multisim 14.0 Full Components

BZX884-B22	BZX884-B75	BZX884-C51	CA0158M
BZX884-B24	BZX884-B7V5	BZX884-C56	CA0158T
BZX884-B27	BZX884-B8V2	BZX884-C5V1	CA0224E
BZX884-B2V4	BZX884-B9V1	BZX884-C62	CA0224M
BZX884-B2V7	BZX884-C10	BZX884-C68	CA0258AE
BZX884-B30	BZX884-C11	BZX884-C6V2	CA0258AM
BZX884-B33	BZX884-C12	BZX884-C75	CA0258AT
BZX884-B36	BZX884-C13	BZX884-C7V5	CA0258E
BZX884-B39	BZX884-C16	BZX884-C8V2	CA0258M
BZX884-B3V0	BZX884-C20	BZX884-C9V1	CA0258T
BZX884-B3V3	BZX884-C22	C232A	CA0324E
BZX884-B3V6	BZX884-C24	C232B	CA0324M
BZX884-B3V9	BZX884-C2V4	C232D	CA0358AE
BZX884-B43	BZX884-C2V7	C232F	CA0358AM
BZX884-B47	BZX884-C30	C232M	CA0358AT
BZX884-B4V3	BZX884-C33	C233A	CA0358E
BZX884-B4V7	BZX884-C36	C233B	CA0358M
BZX884-B51	BZX884-C3V0	C233D	CA0358T
BZX884-B56	BZX884-C3V3	C233F	CA0741E
BZX884-B5V1	BZX884-C3V6	C233M	CA0741T
BZX884-B5V6	BZX884-C3V9	CA0124E	CA1458E
BZX884-B62	BZX884-C43	CA0124M	CA1458T
BZX884-B68	BZX884-C47	CA0158AE	CA2902M
BZX884-B6V2	BZX884-C4V3	CA0158AT	CA2902N
BZX884-B6V8	BZX884-C4V7	CA0158E	CA2904E

Multisim 14.0 Full Components

CA2904M	CA3100T	CA5130AT	CHIRP_VOLTAGE
CA3060E	CA3130E	CA5130E	CLC103AI
CA3078AE	CA3130M	CA5130M	CLC103AM
CA3078AM	CA3130T	CA5130T	CLC111AJE
CA3078AT	CA3140E	CA5160AE	CLC111AJP
CA3078E	CA3140M	CA5160AM	CLC200A8C
CA3078M	CA3140T	CA5260AE	CLC200AI
CA3078T	CA3160E	CA5260AM	CLC200AK
CA3080	CA3160T	CA5260E	CLC200AM
CA3080A	CA3193AE	CA5260M	CLC201
CA3080AE	CA3193AT	CA5420E	CLC203
CA3080AM	CA3193E	CA5420M	CLC220
CA3080E	CA3193T	CA5420T	CLC400A8B
CA3080M	CA3240AE	CA5470E	CLC400A8D
CA3094AE	CA3240AE1	CA5470M	CLC400AIB
CA3094AM	CA3240E	CAP_ELECTROLIT_V IRTUAL	CLC400AID
CA3094AT	CA3240E1		CLC400AJE
CA3094BE	CA3260E	CAPACITOR_POL_R ATED	CLC400AJP
CA3094BM	CA3260T	CAPACITOR_RATED	CLC401A8B
CA3094BT	CA3280E	CAPACITOR_VIRTU AL	CLC401A8D
CA3094E	CA3440AE		CLC401AIB
CA3094M	CA3440M	CD4538BCM	CLC401AID
CA3094T	CA3450E	CD4538BCN	CLC401AJE
CA3100E	CA5130AE	CD4538BCWM	CLC401AJP
CA3100M	CA5130AM	CHIRP_CURRENT	CLC402A8B

Multisim 14.0 Full Components

CLC402A8D	CLC409AJP	CLC420A8D	CLC431A8B
CLC402AID	CLC410A8B	CLC420AIB	CLC431AJE
CLC402AJE	CLC410A8D	CLC420AJE	CLC431AJP
CLC402AJP	CLC410AJE	CLC420AJP	CLC432A8B
CLC404A8D	CLC410AJP	CLC420B8B	CLC432AJE
CLC404AID	CLC411A8B	CLC420B8D	CLC432AJP
CLC404AJE	CLC411AJE	CLC420BIB	CLC440A8B
CLC404AJM5	CLC411AJP	CLC420BJE	CLC440AJE
CLC404AJP	CLC412A8B	CLC420BJP	CLC440AJP
CLC405A8B	CLC412AIB	CLC423AJE	CLC449A8B
CLC405AIB	CLC412AJE	CLC423AJP	CLC449AJE
CLC405AJE	CLC412AJP	CLC425A8B	CLC449AJP
CLC405AJP	CLC414A8B	CLC425AIB	CLC501A8D
CLC406A8B	CLC414A8D	CLC425AJE	CLC501AID
CLC406A8D	CLC414AJE	CLC425AJP	CLC501AJE
CLC406AJE	CLC414AJP	CLC426A8B	CLC501AJP
CLC406AJM5	CLC415A8B	CLC426AIB	CLC502A8D
CLC406AJP	CLC415A8D	CLC426AJE	CLC502AID
CLC407AIB	CLC415AJE	CLC426AJP	CLC502AJE
CLC407AJE	CLC415AJP	CLC428A8B	CLC502AJP
CLC407AJP	CLC416AJE	CLC428AJE	CLC505A8D
CLC409A8D	CLC416AJP	CLC428AJP	CLC505AJE
CLC409AID	CLC417AJE	CLC430A8B	CLC505AJP
CLC409AJE	CLC417AJP	CLC430AJE	CLOCK_CURRENT
CLC409AJM5	CLC420A8B	CLC430AJP	CLOCK_VOLTAGE

Multisim 14.0 Full Components

CM1213A-02SR	CNY17F-3X017	CORELESS_COIL_VIRTUAL	CRYSTAL_VIRTUAL
CNTR_16SBIN	CNY17F-3X019	COUNT_OFF	CS494001-LQFP(144)
CNTR_4ABIN	COMP_4	COUNT_OFF_HOLD	CS494501-TQFP(100)
CNTR_4ADEC	COMPARATOR_IDEAL	COUNT_OFF_RESET	CURRENT_CONTROLLED_CURRENT_SOURCE
CNTR_4BIN_AS	COMPARATOR_VIRTUAL	COUNT_ON	CURRENT_CONTROLLED_SPST
CNTR_4BIN_ASCLR	CONTROL_1A	COUNT_ON_HOLD	CURRENT_CONTROLLED_SPST_ANIMATED
CNTR_4BIN_S	CONTROL_1C	COUNT_ON_RESET	CURRENT_CONTROLLED_VOLTAGE_SOURCE
CNTR_4BIN_SU_D	CONTROL_2A	COUNT_UPDOWN_OFF	CURRENT_LIMITER_BLOCK
CNTR_4BINS_DC	CONTROL_2C	COUNT_UPDOWN_ON	CY37032P44-125AC
CNTR_4SDEC	CONTROL_3A	COUPLED_INDUCTORS	CY37032P44-125AI
CNTR_7BIN	CONTROL_3C	CPH3105-TL-E	CY37032P44-125JC
CNTR_8SBIN	CONTROL_4A	CPH3123-TL-E	CY37032P44-125JI
CNTR_BCD_S	CONTROL_4C	CPH3144-TL-E	CY37032P44-154AC
CNTR_BCD_SDC	CONTROL_NC	CPH3205-TL-E	CY37032P44-154AI
CNTR_BCD_SU_D	CONTROL_NO	CPH3223-TL-E	CY37032P44-154JC
CNTR_BIN_DEC_SU_D	CONTROLLED_ONE_SHOT	CPH3448-TL-H	CY37032P44-200AC
CNTR_JOHNSON	CONVEYOR_BELT	CPH5505-TL-E	CY37032P44-200JC
CNY17F-3	COP87L20CJN	CPH5506-TL-E	CY37032P44-222AC
CNY17F-3X001	COP87L22CJN	CPH6223-TL-E	
CNY17F-3X006	COP87L40CJN	CPH6341-TL-E	
CNY17F-3X007T	COP87L40RJN	CPH6445-TL-E	
CNY17F-3X009T	COP87L42CJN	CPH6531-TL-E	
CNY17F-3X016	COP87L42RJN		

Multisim 14.0 Full Components

CY37032P44-222JC	DC_INTERACTIVE_V OLTAGE	DEC_BCD_10_INV	DIODE
CYPRESS-ULTRA- ISR-HDR	DC_MACHINE_PER MANENT_MAGNET	DEC_BCD_7	DIODE
D_FF	DC_MACHINE_WO UND_FIELD	DEC2_4	DIODE_RATED
D_FF_NEGSR	DC_MACHINE_WO UND_FIELD	DEC3_8	DIP10
D_FF_POSSR	DC_MACHINE_WO UND_FIELD	DEC4_10	DIP12
D_LATCH	DC_POWER	DELAY	DIP14
D_LATCH_NEGSR	DCC010-TB-E	DEM4_16	DIP16
D1N4148	DCD_2TO4	DF06MA-E3/45	DIP18
D44C12G	DCD_3TO8	DF10S/45	DIP20
D44H11G	DCD_4TO16	DF10SA-E3/45	DIP22
D44H8G	DCD_7SEG	DF1510S-E3/77	DIP24
D44H8G	DCD_7SEG_P	DF3A6.8FUT1G	DIP28
D44VH10G	DCD_BARGRAPH	DF6A6.8FUT1G	DIP4
D45C12G	DCD_HEX	DGND	DIP6
D45H11G	DCD_HEX_BLUE	DIGITAL_CLOCK	DIP8
D45H8G	DCD_HEX_DIG_BLU E	DIGITAL_CONSTAN T	DIPSW1
D45VH10G	DCD_HEX_DIG_BLU E	DIGITAL_CONSTAN T	DIPSW10
DAC7642_FP32	DCD_HEX_DIG_GRE EN	DIGITAL_FREQUEN CY_DIVIDER	DIPSW2
DAC7643_FP32	DCD_HEX_DIG_ORA NGE	DIGITAL_HIGH	DIPSW3
DAC8541	DCD_HEX_DIG_ORA NGE	DIGITAL_HIGH	DIPSW4
DAN222M3T5G	DCD_HEX_DIG_RED	DIGITAL_LOW	DIPSW5
DAP222M3T5G	DCD_HEX_DIG_YEL LOW	DIGITAL_PULLDOW N	DIPSW6
DBREAK	DCD_HEX_GREEN	DIGITAL_PULLUP	DIPSW7
DC_CURRENT	DCD_HEX_ORANGE	DIGITAL_STATE_MA CHINE	DIPSW8
DC_INTERACTIVE_C URRENT	DCD_HEX_YELLOW	DIGITAL_STATE_MA CHINE	DIPSW9

Multisim 14.0 Full Components

DIV	DSP1628- TQFP(100)	DTA114EM3T5G	DTC113EM3T5G
DIVIDER		DTA114TET1G	DTC114EET1G
DP8421A	DSP16410B- PBGA(208)	DTA114TM3T5G	DTC114EM3T5G
DP8421A_LCC68	DSUB15F	DTA114YET1G	DTC114TET1G
DP8422A_LCC84	DSUB15F-VGA	DTA114YM3T5G	DTC114TM3T5G
DPDT_DB	DSUB15M	DTA115EET1G	DTC114YET1G
DPDT_SB	DSUB15M-VGA	DTA115EM3T5G	DTC115EET1G
DPST_2NC_DB	DSUB25F	DTA115TET1G	DTC115EM3T5G
DPST_2NC_SB	DSUB25M	DTA115TM3T5G	DTC115TET1G
DPST_2NO_DB	DSUB37F	DTA123EM3T5G	DTC115TM3T5G
DPST_2NO_SB	DSUB37M	DTA123TET1G	DTC123EM3T5G
DRV103H	DSUB9F	DTA123TM3T5G	DTC123JET1G
DRV103U	DSUB9M	DTA124EET1G	DTC123JM3T5G
DRV104PWP	DSWPK_10	DTA124EM3T5G	DTC123TET1G
DS1846_SO20	DSWPK_2	DTA124XM3T5G	DTC123TM3T5G
DS80C310_LCC44	DSWPK_3	DTA143EET1G	DTC124EET1G
DS80C320_LCC44	DSWPK_4	DTA143EM3T5G	DTC124EM3T5G
DS80C323_LCC44	DSWPK_5	DTA143ZET1G	DTC124XET1G
DS83C520_LCC44	DSWPK_6	DTA143ZM3T5G	DTC124XM3T5G
DS83C530_FP52	DSWPK_7	DTA144EET1G	DTC143EET1G
DS87C520_LCC44	DSWPK_8	DTA144EM3T5G	DTC143EM3T5G
DS87C530_FP52	DSWPK_9	DTA144TET1G	DTC143TM3T5G
DSP16210- TQFP(144)	DTA113EET1G	DTA144TM3T5G	DTC143ZET1G
	DTA113EM3T5G	DTA144WM3T5G	DTC143ZM3T5G
DSP1628- BQFP(100)	DTA114EET1G	DTC113EET1G	DTC144EET1G

Multisim 14.0 Full Components

DTC144EM3T5G	EDR2H1A24	EL2411CN	EMR011A06
DTC144TET1G	EGF1D-E3/67A	EL2411CS	EMR011A08
DTC144TM3T5G	EGF1T-E3/67A	EL2500/EL	EMR011A09
DTC144WM3T5G	EGP10D-E3/54	EL2520/EL	EMR011A12
DTMF_KEYPAD	EGP10G-E3/54	EL2600/EL	EMR011A24
ECG6407	EGP50D-E3/54	EL2620/EL	EMR011B03
ECG6408	EGP50G-E3/54	EL4089CN	EMR011B05
ECG6411	EL2006CG	EL4089CS	EMR011B06
ECG6412	EL2006G	EL4430CN	EMR011B08
ECH8102-TL-H	EL2006G/883B	EL4430CS	EMR011B09
ECH8649-TL-H	EL2022/EL	EL4451CN	EMR011B12
ECH8651R-R-TL-H	EL2022CG	EL4451CS	EMR011B24
ECH8651R-TL-H	EL2022G	EL4452CN	EMR021A03
ECH8652-TL-H	EL2157CN	EL4452CS	EMR021A05
ECH8653-TL-H	EL2157CS	ELH0032G/883B	EMR021A06
ECH8654-TL-H	EL2210CN	ELH0101K/883B	EMR021A08
ECH8657-TL-H	EL2210CS	EMC2DXV5T1G	EMR021A09
ECH8660-TL-H	EL2211CN	EMC3DXV5T1G	EMR021A12
ECH8662-TL-H	EL2211CS	EMC3DXV5T5G	EMR021A24
EDF1DS-E3/45	EL2310CN	EMC4DXV5T1G	EMR021B03
EDR201A05	EL2310CS	EMC5DXV5T1G	EMR021B05
EDR201A12	EL2311CN	EMH1303-TL-E	EMR021B06
EDR201A24	EL2311CS	EMH1405-TL-H	EMR021B08
EDR2H1A05	EL2410CN	EMR011A03	EMR021B09
EDR2H1A12	EL2410CS	EMR011A05	EMR021B12

Multisim 14.0 Full Components

EMR021B24	EMR121B08	EMR161A03	ENERGIZING_COIL_ TIMED
EMR031A03	EMR121B09	EMR161A05	EP2015ACN
EMR031A05	EMR121B12	EMR161A06	EP2015CM
EMR031A06	EMR121B24	EMR161A08	EP2015CN
EMR031A08	EMR131A03	EMR161A09	EPC2001
EMR031A09	EMR131A05	EMR161A12	EPC2007
EMR031A12	EMR131A06	EMR171A03	EPC2010
EMR031A24	EMR131A08	EMR171A05	EPC2012
EMR031B03	EMR131A09	EMR171A06	EPC2014
EMR031B05	EMR131A12	EMR171A08	EPC2015
EMR031B06	EMR131A24	EMR171A09	EPC2016
EMR031B08	EMR131B03	EMR171A12	EPC2018
EMR031B09	EMR131B05	EMR171A24	EPC2019
EMR031B12	EMR131B06	EMX1DXV6T1G	EPC2020
EMR031B24	EMR131B08	EMX1DXV6T5G	EPC2021
EMR121A03	EMR131B09	EN2016CM	EPC2022
EMR121A05	EMR131B12	EN2016CN	EPC2023
EMR121A06	EMR131B24	ENC_10TO4	EPC2024
EMR121A08	EMR151A03	ENC_8TO3	EPC2025
EMR121A09	EMR151A05	ENC_8TO3S	EPC2100
EMR121A12	EMR151A06	ENC10_4	EPC2801
EMR121A24	EMR151A08	ENC8_3	EPC2815
EMR121B03	EMR151A09	ENERGIZING_COIL	EPC2818
EMR121B05	EMR151A12	ENERGIZING_COIL_ AC	EPC8002
EMR121B06	EMR151A24		

Multisim 14.0 Full Components

EPC8003	EPM7096-PLCC(68)	ESD0P2RF-02LRH	ESD8V0R1B-02EL
EPC8004	EPM7096-PLCC(84)	ESD0P2RF-02LS	ESD8V0R1B-02ELS
EPC8005	EPM7096- PQFP(100)	ESD11L5.0DT5G	ESD9B3.3ST5G
EPC8007		ESD18VU1B-02LRH	ESD9B5.0ST5G
EPC8008	EPM7128AE- PLCC(84)	ESD18VU1B-02LS	ESD9C3.3ST5G
EPC8009	EPM7128AE- TQFP(100)	ESD3V3U4ULC	ESD9C5.0ST5G
EPC8010		ESD5B5.0ST1G	ESD9L5.0ST5G
EPM7032-PLCC(44)	EPM7128AE- TQFP(144)	ESD5V3L1B-02LS	ESD9X12ST5G
EPM7032-PQFP(44)		ESD5V3U4U-HDMI	ESD9X3.3ST5G
EPM7032S- PLCC(44)	EPM7128A- PLCC(84)	ESD5Z12T1G	ESD9X5.0ST5G
EPM7032S- TQFP(44)	EPM7128A- TQFP(100)	ESD5Z2.5T1G	ESDR0502NMUTAG
EPM7032-TQFP(44)	EPM7128A- TQFP(144)	ESD5Z3.3T1G	ESDR0502NMUTBG
EPM7064-PLCC(44)	EPM7512AE- PQFP(208)	ESD5Z5.0T1G	ESDR0544MDMR4G
EPM7064-PLCC(68)		ESD5Z6.0T1G	ESH1PD-E3/84A
EPM7064-PLCC(84)	EPM7512AE- TQFP(144)	ESD5Z7.0T1G	EVAL-SDP-CB1Z
EPM7064- PQFP(100)	ES1B-E3/61T	ESD5Z7.0T5G	EVAL-SDP- CH1Z_FMC
EPM7064S- PLCC(44)	ES1C-E3/61T	ESD7004MUTAG	EVAL-SDP-CS1Z
EPM7064S- PLCC(84)	ES1D-E3/61T	ESD7008MUTAG	EXPONENTIAL_CUR RENT
	ES1PD-E3/84A	ESD7016MUTAG	EXPONENTIAL_VOL TAGE
EPM7064S- TQFP(100)	ES2B-E3/52T	ESD7104MUTAG	
EPM7064S- TQFP(44)	ES2C-E3/52T	ESD7951ST5G	F1007
	ES2D-E3/52T	ESD7C3.3DT5G	F1008
	ES3D-E3/57T	ESD7C5.0DT5G	F1020
EPM7064-TQFP(44)		ESD8004MUTAG	
		ESD8040MUTAG	

Multisim 14.0 Full Components

FAST_1A	FLOW_NO	FMMT717	FREQUENCY_TABLE _FUNCTION
FAST_2A	FM_CURRENT	FMMT718	FSK_VOLTAGE
FAST_3A	FM_VOLTAGE	FMMT720	FULL_ADDER
FAST_4A	FMMD2835	FMMT722	FUSE
FCN-268D024- G/10-R	FMMD2836	FMMT723	FUSE_RATED
FCX458	FMMD2837	FMMT918	FUSE_VIRTUAL
FCX558	FMMD2838	FMMTA20	FX2-100S- 1.27DS(71)
FCX649	FMMD6050	FMMTA70	FX8-120P-SV1(91)
FCX749	FMMD6100	FMMTH10	FX8-120S-SV(21)
FEP16DT-E3/45	FMMD7000	FMMV105G	FZT604
FEP30GP-E3/45	FMMD914	FMMV109	FZT605
FEP30JPE3/45	FMMT38B	FMMV2101	FZT649
FES16BT-E3/45	FMMT489	FMMV2102	FZT651
FES16GT-E3/45	FMMT491A	FMMV2103	FZT657
FES8DT-E3/45	FMMT5179	FMMV2104	FZT658
FF_D_CO	FMMT549	FMMV2105	FZT688B
FF_D_PCLR_CO	FMMT589	FMMV2106	FZT689B
FF_D4_CLR_CO	FMMT591A	FMMV2107	FZT690B
FF_JK_NSCLR_CO	FMMT597	FMMV2108	FZT692B
FF_JK_PSCLR_CO	FMMT597Q	FMMV2109	FZT694B
FF_T_CLR_CO	FMMT617	FMMV3102	FZT696B
FLOAT_NC	FMMT618	FOOT_NC	FZT705
FLOAT_NO	FMMT619	FOOT_NO	FZT749
FLOW_NC	FMMT624	FREQ_DIVIDER	FZT751
	FMMT625		

Multisim 14.0 Full Components

FZT757	GI250-1	GLL4742	GP02-35
FZT758	GI250-2	GLL4743	GP02-40
FZT788A	GI250-3	GLL4744	GP08A
FZT788B	GI250-4	GLL4745	GP08B
FZT789A	GI751-E3/54	GLL4746	GP08D
FZT790A	GI810	GLL4747	GP08G
FZT792A	GI811	GLL4748	GP08J
G3SBA60-E3/51	GI812	GLL4749	GP10A
GaAsFET_N	GI814	GLL4750	GP10B
GaAsFET_P	GI816	GLL4751	GP10D
GAIN_2_PIN	GI817	GLL4752	GP10G
GBPC3506W-E4/51	GI818	GLL4753	GP10J
GBU4G-E3/45	GL34A	GLL4754	GP10K
GBU4M-E3/51	GL34B	GLL4755	GP10M
GBU6G-E3/45	GL34D	GLL4756	GP10N
GBU6M-E3/45	GL34G	GLL4757	GP10Q
GEN_CNTR_4ABIN	GL34G-E3/98	GLL4758	GP10T
GF1A	GL34J	GLL4759	GP10V
GF1B	GLL4735	GLL4760	GP10W
GF1D	GLL4736	GLL4761	GP10Y
GF1G	GLL4737	GLL4762	GP10Y-E3/54
GF1G-E3/67A	GLL4738	GLL4763	GP15A
GF1J	GLL4739	GP02-20	GP15B
GF1K	GLL4740	GP02-25	GP15D
GF1M	GLL4741	GP02-30	GP15G

Multisim 14.0 Full Components

GP15J	GSB3211311WEU	HA1-5190-2	HA2-5101-2
GP15K	GSIB1580-E3/45	HA2-2500-2	HA2-5102-2
GP15M	GSIB2560-E3/45	HA2-2502-2	HA2-5102-5
GP20A	GTO	HA2-2510-2	HA2-5130-5
GP20B	HA1-2539-2	HA2-2512-2	HA2-5135-5
GP20D	HA1-2539-5	HA2-2515-2	HA2-5142-2
GP20G	HA1-2540-2	HA2-2520-2	HA2-5142-5
GP20J	HA1-2540-5	HA2-2522-2	HA2-5147-2
GP30A	HA1-2541-2	HA2-2525-5	HA2-5147-5
GP30B	HA1-2541-5	HA2-2529-2	HA2-5160-2
GP30D	HA1-2542-2	HA2-2529-5	HA2-5160-5
GP30G	HA1-2542-5	HA2-2541-2	HA2-5162-5
GP30J	HA1-2839-5	HA2-2541-5	HA2-5170-2
GP30K	HA1-2840-5	HA2-2542-2	HA2-5170-5
GP30M	HA1-2840-9	HA2-2542-5	HA2-5190-2
GRAPH_LCD_L	HA1-2850-5	HA2-2544-2	HA2-5221-5
GRAPH_LCD_M	HA1-2850-9	HA2-2548-5	HA2-7712A-5
GRAPH_LCD_S	HA1-4741-2	HA2-2548-9	HA2-7712A-9
GROUND	HA1-4741-5	HA2-2600-2	HA2-7712B-5
GROUND_REF1	HA1-5104-2	HA2-2602-2	HA2-7712B-9
GROUND_REF2	HA1-5104-5	HA2-2605-5	HA3-2444-5
GROUND_REF3	HA1-5114-2	HA2-2620-2	HA3-2444-9
GROUND_REF4	HA1-5114-5	HA2-2622-2	HA3-2525-5
GROUND_REF5	HA1-5134-2	HA2-2625-5	HA3-2529-5
GSB311A41EU	HA1-5134-5	HA2-2640-2	HA3-2539-5

Multisim 14.0 Full Components

HA3-2539C-5	HA3-5127-5	HA7-2515-2	HA7-5127-2
HA3-2540-5	HA3-5127A-5	HA7-2520-2	HA7-5127-5
HA3-2542-5	HA3-5142-5	HA7-2522-2	HA7-5127A-2
HA3-2544-5	HA3-5147-5	HA7-2525-5	HA7-5127A-5
HA3-2544C-5	HA3-5177-5	HA7-2529-5	HA7-5130-2
HA3-2548-5	HA3-5221-5	HA7-2544-2	HA7-5130-5
HA3-2605-5	HA3-5222-5	HA7-2544-5	HA7-5135-2
HA3-2625-5	HA3-5232-5	HA7-2548-5	HA7-5135-5
HA3-2839-5	HA3-5232-9	HA7-2600-2	HA7-5137-2
HA3-2839-9	HA3-7712A-5	HA7-2602-2	HA7-5137-5
HA3-2840-5	HA3-7712A-9	HA7-2605-5	HA7-5142-2
HA3-2840-9	HA3-7712B-5	HA7-2620-2	HA7-5142-5
HA3-2841-5	HA3-7712B-9	HA7-2622-2	HA7-5147-2
HA3-2841-9	HA3B2840-5	HA7-2625-5	HA7-5147-5
HA3-2842-5	HA3B2840-9	HA7-2640-2	HA7-5170-2
HA3-2842-9	HA3B2841-5	HA7-2645-5	HA7-5170-5
HA3-2850-5	HA3B2841-9	HA7-2840-5	HA7-5177-5
HA3-2850-9	HA3B2842-5	HA7-2840-9	HA7-5221-5
HA3-4741-5	HA3B2842-9	HA7-2850-5	HA7-5221-9
HA3-5101-5	HA3B2850-5	HA7-2850-9	HA7-5222-5
HA3-5102-5	HA3B2850-9	HA7-5101-2	HA7-5222-9
HA3-5104-5	HA4P2525-5	HA7-5102-2	HA9P2444-5
HA3-5111-5	HA7-2500-2	HA7-5102-5	HA9P2444-9
HA3-5112-5	HA7-2510-2	HA7-5111-2	HA9P2529-5
HA3-5114-5	HA7-2512-2	HA7-5112-2	HA9P2539-5

Multisim 14.0 Full Components

HA9P2539-9	HA9P5111-9	HC-49/US_11MHz	HCPL-0302-060E
HA9P2540-5	HA9P5112-5	HC-49/US_15MHz	HCPL-0314-000E
HA9P2544-5	HA9P5112-9	HC-49/US_25MHz	HCPL-0314-060E
HA9P2544-9	HA9P5114-5	HC-49/US_40MHz	HCPL-0454-000E
HA9P2544C-5	HA9P5114-9	HC-49/US_5MHz	HCPL-0454-060E
HA9P2544C-9	HA9P5127-5	HC-49/US_7MHz	HCPL-0466-000E
HA9P2548-5	HA9P5137-5	HCNR200	HCPL-0466-060E
HA9P2605-5	HA9P5142-9	HCNR200-000E	HCPL-0501-500E
HA9P2625-5	HA9P5221-5	HCNR200-050E	HCPL-0501-560E
HA9P2840-5	HA9P5222-5	HCNR200-300E	HCPL0631
HA9P2840-9	HA9P5222-9	HCNR200-350E	HCPL-063L-000E
HA9P2841-5	HA9P5232-5	HCNR201	HCPL-063L-060E
HA9P2841-9	HA9P5232-9	HCNW136-000E	HCPL-0701-000E
HA9P2842-5	HA9P7712B-5	HCNW136-300E	HCPL-0701-060E
HA9P2842-9	HA9P7712B-9	HCNW139-000E	HCPL-181-000E
HA9P2850-5	HALF_ADDER	HCNW139-300E	HCPL-181-060E
HA9P2850-9	HC-49/U_1.5MHz	HCNW2201-000E	HCPL-2200-000E
HA9P4741-9	HC-49/U_11MHz	HCNW2201-300E	HCPL-2200-300E
HA9P5101-5	HC-49/U_15MHz	HCNW3120-000E	HCPL-2201-000E
HA9P5101-9	HC-49/U_25MHz	HCNW3120-300E	HCPL-2201-060E
HA9P5102-5	HC-49/U_3MHz	HCPL-0201-000E	HCPL-2201-300E
HA9P5102-9	HC-49/U_40MHz	HCPL-0201-060E	HCPL-2201-360E
HA9P5104-5	HC-49/U_5MHz	HCPL-0211-000E	HCPL-2202-000E
HA9P5104-9	HC-49/U_7MHz	HCPL-0211-060E	HCPL-2202-060E
HA9P5111-5	HC-49/U_80MHz	HCPL-0302-000E	HCPL-2202-300E

Multisim 14.0 Full Components

HCPL-2202-360E	HCPL-3020-300E	HCPL-J312-300E	HDR1X5
HCPL-2211-000E	HCPL-3120-000E	HD4A	HDR1X6
HCPL-2211-060E	HCPL-3120-060E	HD64F2134FA20	HDR1X7
HCPL-2211-300E	HCPL-3120-300E	HD64F2134TF20	HDR1X8
HCPL-2211-360E	HCPL-3120-360E	HD64F2134VFA10	HDR1X9
HCPL-2212-000E	HCPL-3140-000E	HD64F2134VTF10	HDR2X10
HCPL-2212-060E	HCPL-3140-060E	HDR1X10	HDR2X11
HCPL-2212-300E	HCPL-3140-300E	HDR1X11	HDR2X12
HCPL-2212-360E	HCPL-3140-360E	HDR1X12	HDR2X13
HCPL-2219-000E	HCPL-316J-000E	HDR1X13	HDR2X14
HCPL-2219-060E	HCPL-4504-000E	HDR1X14	HDR2X15
HCPL-2219-300E	HCPL-4504-020E	HDR1X15	HDR2X16
HCPL-2219-360E	HCPL-4504-060E	HDR1X16	HDR2X17
HCPL-2231-000E	HCPL-4504-300E	HDR1X17	HDR2X18
HCPL-2231-300E	HCPL-4504-320E	HDR1X18	HDR2X19
HCPL-2232-000E	HCPL-4504-360E	HDR1X19	HDR2X2
HCPL-2232-300E	HCPL-4506-000E	HDR1X2	HDR2X20
HCPL-263L-000E	HCPL-4506-020E	HDR1X20	HDR2X21
HCPL-263L-020E	HCPL-4506-060E	HDR1X21	HDR2X22
HCPL-263L-060E	HCPL-4506-300E	HDR1X22	HDR2X23
HCPL-263L-300E	HCPL-4506-320E	HDR1X23	HDR2X24
HCPL-263L-320E	HCPL-4506-360E	HDR1X24	HDR2X25
HCPL-263L-560E	HCPL-7800-000E	HDR1X25	HDR2X3
HCPL-3020-000E	HCPL-7800-300E	HDR1X3	HDR2X4
HCPL-3020-060E	HCPL-J312-000E	HDR1X4	HDR2X5

Multisim 14.0 Full Components

HDR2X6	HFA3-0001-5	HMA510GM-75/833	ICL7650SIJD
HDR2X7	HFA3-0001-9		ICL7650SIPA-1
HDR2X8	HFA3-0002-5	HOLDING_TANK	ICL7650SIPD
HDR2X9	HFA3-0002-9	HSDL-5400	ICL7650SITV-1
HELD_CLOSED_LIMIT	HFA3-0005-5	HSDL-5420	ICL7650SMJD
	HFA3-0005-9	HSDL-5420#031	ICL7650SMTV-1
HELD_OPEN_LIMIT	HFA30PA60C	HSP43124PC-33	ICL7652
HF30ACC201209	HFA7-0002-5	HSP43124PC-45	ICL7652D
HF30ACC321611	HFA7-0002-9	HSP43168GM-25/883	ICL7652P
HF30ACC322513	HFA7-0005-5	HSP43168GM-33/883	ICM7555ESA+
HF30ACC453215	HFA7-0005-9		ICM7555IJA+
HF50ACC201209	HFA9P0001-5	HSP45240GM-25/883	ICM7555IPA+
HF50ACC321611	HFA9P0002-5		ICM7555ISA+
HF50ACC322513	HFA9P0002-9	HSP45240GM-33/883	ICM7555ITV
HF50ACC453215	HFA9P0005-5	HSP45240GM-40/883	ICM7555MJA
HF70ACC201209	HFA9P0005-9		ICM7555MTV
HF70ACC321611	HM1-65642-883	ICL7611ACPA	ICM7556IPD+
HF70ACC322513	HM1-65642B-883	ICL7611ACTV	ICM7556ISD+
HF70ACC453215	HM1-65642C-883	ICL7611AMTV	ICM7556MJD+
HFA1-0001-5	HM4-65642-883	ICL7611DCBA	IDAC
HFA1-0001-9	HM4-65642B-883	ICL7650SCBA-1	IDAC16
HFA2-0002-5	HM6116A120	ICL7650SCBD	IDH02G65C5
HFA2-0002-9	HMA510GM-55/833	ICL7650SCPA	IDH03G65C5
HFA2-0005-5		ICL7650SCPD	IDH04G65C5
HFA2-0005-9	HMA510GM-65/833	ICL7650SCTV-1	IDH05G65C5

Multisim 14.0 Full Components

IDH06G65C5	IDT7210L55G	INA157UA	INA2132U
IDH08G65C5	IDT7210L55J	INA159AID	INA2132UA
IDH09G65C5	IDT7210L65C	INA163UA	INA213AIDCKR
IDH10G65C5	IDT7210L65F	INA168NA	INA213AIDCKT
IDH12G65C5	IDT7210L65G	INA169NA	INA213AIRSWR
IDH16G65C5	IDT7210L65J	INA170EA	INA213BIDCKR
IDH20G65C5	IDW10S120	INA193AID	INA213BIRSWR
IDT7210L20C	IDW15S120	INA194AID	INA214AIDCKR
IDT7210L20F	IDW20S120	INA195AID	INA214AIRSWR
IDT7210L20G	IDW30S120	INA201AID	INA214BIDCKR
IDT7210L20J	ILLUMINATED_PB	INA201AIDGKR	INA214BIRSWR
IDT7210L25C	IMSA110-G20S	INA206AID	INA216A2RSWR
IDT7210L25F	INA105_CMP	INA206AIPW	INA216A2YFFR
IDT7210L25G	INA133U	INA210AIDCKR	INA216A3RSWR
IDT7210L25J	INA133UA	INA210AIRSWR	INA216A3YFFR
IDT7210L35C	INA138NA	INA210BIDCKR	INA216A4RSWR
IDT7210L35F	INA143U	INA210BIRSWR	INA216A4YFFR
IDT7210L35G	INA143UA	INA211AIDCKR	INA270AID
IDT7210L35J	INA145UA	INA211BIDCKR	INA271AID
IDT7210L45C	INA146UA	INA2126E/250	INA321E
IDT7210L45F	INA148UA	INA2126EA/250	INA321EA
IDT7210L45G	INA152EA/250	INA2126P	INA322EA
IDT7210L45J	INA154U	INA2126U	INA326EA
IDT7210L55C	INA154UA	INA212AIDCKR	INA327EA
IDT7210L55F	INA157U	INA212BIDCKR	INA331AIDGK

Multisim 14.0 Full Components

INA331IDGK	IPA126N10N3 G	IPA60R280C6	IPA65R420CFD
INA332IDGK	IPA180N10N3 G	IPA60R280E6	IPA65R600C6
INA333AIDGKR	IPA50R140CP	IPA60R299CP	IPA65R600E6
INA333AIDRGR	IPA50R190CE	IPA60R380C6	IPA65R660CFD
INDICATOR	IPA50R199CP	IPA60R380E6	IPA90R1K0C3
INDUCTOR_ADVANCED	IPA50R250CP	IPA60R385CP	IPA90R1K2C3
Inductor_Lossy	IPA50R280CE	IPA60R520C6	IPA90R340C3
	IPA50R299CP	IPA60R520E6	IPA90R500C3
INDUCTOR_RATED	IPA50R350CP	IPA60R600C6	IPA90R800C3
INDUCTOR_VIRTUAL	IPA50R380CE	IPA60R600E6	IPB009N03L G
	IPA50R399CP	IPA60R950C6	IPB010N06N
INTERACTIVE_DIGITAL_CONSTANT	IPA50R500CE	IPA65R045C7	IPB011N04L G
	IPA50R520CP	IPA65R065C7	IPB011N04N G
INV	IPA50R650CE	IPA65R095C7	IPB014N06N
IPA028N08N3 G	IPA50R800CE	IPA65R125C7	IPB015N04L G
IPA030N10N3 G	IPA50R950CE	IPA65R190C6	IPB015N04N G
IPA032N06N3 G	IPA60R099C6	IPA65R190C7	IPB016N06L3 G
IPA037N08N3 G	IPA60R125C6	IPA65R190CFD	IPB017N06N3 G
IPA045N10N3 G	IPA60R125CP	IPA65R190E6	IPB019N06L3 G
IPA057N06N3 G	IPA60R160C6	IPA65R225C7	IPB019N08N3 G
IPA075N15N3 G	IPA60R165CP	IPA65R280C6	IPB020N04N G
IPA086N10N3 G	IPA60R190C6	IPA65R280E6	IPB020NE7N3 G
IPA093N06N3 G	IPA60R190E6	IPA65R310CFD	IPB021N06N3 G
IPA100N08N3 G	IPA60R199CP	IPA65R380C6	IPB022N04L G
IPA105N15N3 G	IPA60R250CP	IPA65R380E6	IPB023N04N G

Multisim 14.0 Full Components

IPB023N06N3 G	IPB054N06N3 G	IPB200N25N3 G	IPB65R190C7
IPB025N08N3 G	IPB054N08N3 G	IPB230N06L3 G	IPB65R190CFD
IPB025N10N3 G	IPB055N03L G	IPB260N06N3 G	IPB65R190CFDA
IPB026N06N	IPB057N06N	IPB26CN10N G	IPB65R225C7
IPB027N10N3 G	IPB065N03L G	IPB320N20N3 G	IPB65R310CFDA
IPB029N06N3 G	IPB065N15N3 G	IPB34CN10N G	IPB65R660CFD
IPB030N08N3 G	IPB067N08N3 G	IPB50CN10N G	IPB65R660CFDA
IPB031NE7N3 G	IPB072N15N3 G	IPB50R140CP	IPD025N06N
IPB034N03L G	IPB075N04L G	IPB50R199CP	IPD031N03L G
IPB034N06L3 G	IPB080N03L G	IPB50R250CP	IPD031N06L3 G
IPB034N06N3 G	IPB081N06L3 G	IPB50R299CP	IPD034N06N3 G
IPB035N08N3 G	IPB083N10N3 G	IPB530N15N3 G	IPD035N06L3 G
IPB036N12N3 G	IPB090N06N3 G	IPB600N25N3 G	IPD036N04L G
IPB037N06N3 G	IPB093N04L G	IPB60R099CP	IPD038N04N G
IPB038N12N3 G	IPB096N03L G	IPB60R125CP	IPD038N06N3 G
IPB039N04L G	IPB097N08N3 G	IPB60R165CP	IPD040N03L G
IPB039N10N3 G	IPB107N20N3 G	IPB60R199CP	IPD042P03L3 G
IPB041N04N G	IPB107N20NA	IPB60R250CP	IPD048N06L3 G
IPB042N03L G	IPB108N15N3 G	IPB60R385CP	IPD050N03L G
IPB042N10N3 G	IPB114N03L G	IPB65R045C7	IPD053N06N
IPB048N06L G	IPB123N10N3 G	IPB65R065C7	IPD053N06N3 G
IPB049N06L3 G	IPB136N08N3 G	IPB65R095C7	IPD053N08N3 G
IPB049NE7N3 G	IPB144N12N3 G	IPB65R110CFDA	IPD060N03L G
IPB050N06N G	IPB147N03L G	IPB65R125C7	IPD068N10N3 G
IPB052N04N G	IPB200N15N3 G	IPB65R150CFDA	IPD068P03L3 G

Multisim 14.0 Full Components

IPD075N03L G	IPD33CN10N G	IPD65R225C7	IPI052NE7N3 G
IPD079N06L3 G	IPD350N06L G	IPD65R380C6	IPI057N08N3 G
IPD082N10N3 G	IPD400N06N G	IPD65R380E6	IPI070N08N3 G
IPD088N04L G	IPD50R1K4CE	IPD65R420CFD	IPI072N10N3 G
IPD088N06N3 G	IPD50R280CE	IPD65R420CFDA	IPI075N15N3 G
IPD090N03L G	IPD50R2K0CE	IPD65R600C6	IPI076N12N3 G
IPD096N08N3 G	IPD50R380CE	IPD65R600E6	IPI084N06L3 G
IPD105N03L G	IPD50R399CP	IPD65R660CFD	IPI086N10N3 G
IPD105N04L G	IPD50R3K0CE	IPD78CN10N G	IPI100N08N3 G
IPD110N12N3 G	IPD50R500CE	IPD800N06N G	IPI110N20N3 G
IPD122N10N3 G	IPD50R520CP	IPD90R1K2C3	IPI111N15N3 G
IPD127N06L G	IPD50R650CE	IPI020N06N	IPI126N10N3 G
IPD12CN10N G	IPD50R800CE	IPI023NE7N3 G	IPI139N08N3 G
IPD135N03L G	IPD50R950CE	IPI024N06N3 G	IPI147N12N3 G
IPD135N08N3 G	IPD530N15N3 G	IPI028N08N3 G	IPI180N10N3 G
IPD144N06N G	IPD600N25N3 G	IPI029N06N	IPI200N15N3 G
IPD160N04L G	IPD60R1K4C6	IPI030N10N3 G	IPI200N25N3 G
IPD170N04N G	IPD60R2K0C6	IPI032N06N3 G	IPI26CN10N G
IPD180N10N3 G	IPD60R380C6	IPI034NE7N3 G	IPI320N20N3 G
IPD200N15N3 G	IPD60R520C6	IPI037N06L3 G	IPI35CN10N G
IPD220N06L3 G	IPD60R600C6	IPI037N08N3 G	IPI50CN10N G
IPD230N06N G	IPD60R600E6	IPI040N06N3 G	IPI50R350CP
IPD250N06N3 G	IPD60R950C6	IPI041N12N3 G	IPI530N15N3 G
IPD25CN10N G	IPD640N06L G	IPI045N10N3 G	IPI600N25N3 G
IPD320N20N3 G	IPD65R190C7	IPI04CN10N G	IPI60R250CP

Multisim 14.0 Full Components

IPI80CN10N G	IPP037N06L3 G	IPP080N03L G	IPP260N06N3 G
IPI90R1K0C3	IPP037N08N3 G	IPP084N06L3 G	IPP26CN10N G
IPI90R1K2C3	IPP040N06N	IPP085N06L G	IPP320N20N3 G
IPI90R500C3	IPP040N06N3 G	IPP086N10N3 G	IPP50CN10N G
IPI90R800C3	IPP041N04N G	IPP08CN10L G	IPP50R140CP
IPL60R199CP	IPP041N12N3 G	IPP093N06N3 G	IPP50R190CE
IPL60R299CP	IPP042N03L G	IPP096N03L G	IPP50R199CP
IPL60R385CP	IPP045N10N3 G	IPP100N08N3 G	IPP50R250CP
IPL65R070C7	IPP048N12N3 G	IPP110N20N3 G	IPP50R280CE
IPL65R099C7	IPP04CN10N G	IPP110N20NA	IPP50R299CP
IPL65R130C7	IPP052N06L3 G	IPP111N15N3 G	IPP50R350CP
IPL65R195C7	IPP052NE7N3 G	IPP114N03L G	IPP50R380CE
IPL65R230C7	IPP055N03L G	IPP114N12N3 G	IPP50R399CP
IPP015N04N G	IPP057N06N3 G	IPP120N06N G	IPP50R500CE
IPP020N06N	IPP057N08N3 G	IPP126N10N3 G	IPP50R520CP
IPP023N04N	IPP05CN10L G	IPP12CN10L G	IPP530N15N3 G
IPP023N04N G	IPP05CN10N G	IPP139N08N3 G	IPP600N25N3 G
IPP023NE7N3 G	IPP060N06N	IPP147N03L G	IPP60R099C6
IPP024N06N3 G	IPP062NE7N3 G	IPP147N12N3 G	IPP60R099CP
IPP028N08N3 G	IPP065N03L G	IPP16CN10L G	IPP60R125C6
IPP029N06N	IPP06CN10L G	IPP16CN10N G	IPP60R125CP
IPP030N10N3 G	IPP070N08N3 G	IPP180N10N3 G	IPP60R160C6
IPP032N06N3 G	IPP072N10N3 G	IPP200N15N3 G	IPP60R165CP
IPP034N03L G	IPP075N15N3 G	IPP200N25N3 G	IPP60R190C6
IPP034NE7N3 G	IPP076N12N3 G	IPP230N06L3 G	IPP60R190E6

Multisim 14.0 Full Components

IPP60R199CP	IPP65R190E6	IPS105N03L G	IPW60R125CP
IPP60R1K4C6	IPP65R225C7	IPS110N12N3 G	IPW60R160C6
IPP60R250CP	IPP65R280C6	IPS118N10N G	IPW60R165CP
IPP60R280C6	IPP65R280E6	IPS12CN10L G	IPW60R190C6
IPP60R280E6	IPP65R310CFD	IPS135N03L G	IPW60R190E6
IPP60R299CP	IPP65R310CFDA	IPS50R520CP	IPW60R199CP
IPP60R380C6	IPP65R380C6	IPT004N03L	IPW60R250CP
IPP60R380E6	IPP65R380E6	IPT007N06N	IPW60R280C6
IPP60R385CP	IPP65R420CFD	IPT020N10N3	IPW60R280E6
IPP60R520C6	IPP65R600C6	IPT059N15N3	IPW65R019C7
IPP60R520E6	IPP65R600E6	IPU135N08N3 G	IPW65R037C6
IPP60R600C6	IPP65R660CFD	IPU50R1K4CE	IPW65R041CFD
IPP60R600E6	IPP65R660CFDA	IPU50R2K0CE	IPW65R045C7
IPP60R950C6	IPP80CN10N G	IPU50R3K0CE	IPW65R048CFDA
IPP65R045C7	IPP90R1K0C3	IPU50R950CE	IPW65R065C7
IPP65R065C7	IPP90R1K2C3	IPW50R190CE	IPW65R070C6
IPP65R095C7	IPP90R340C3	IPW50R199CP	IPW65R080CFD
IPP65R110CFD	IPP90R500C3	IPW50R280CE	IPW65R080CFDA
IPP65R110CFDA	IPP90R800C3	IPW60R041C6	IPW65R095C7
IPP65R125C7	IPS031N03L G	IPW60R045CP	IPW65R110CFDA
IPP65R150CFDA	IPS040N03L G	IPW60R070C6	IPW65R125C7
IPP65R190C6	IPS050N03L G	IPW60R075CP	IPW65R150CFDA
IPP65R190C7	IPS060N03L G	IPW60R099C6	IPW65R190C6
IPP65R190CFD	IPS075N03L G	IPW60R099CP	IPW65R190C7
IPP65R190CFDA	IPS090N03L G	IPW60R125C6	IPW65R190CFDA

Multisim 14.0 Full Components

IPW65R190E6	IR2106PBF	IR21363PBF	IRF1324STRL-7PP
IPW65R280C6	IR2106SPBF	IR21363SPBF	IRF1404ZPBF
IPW65R280E6	IR21084PBF	IR21365PBF	IRF250
IPW90R120C3	IR21084SPBF	IR21365SPBF	IRF2505S
IPW90R1K0C3	IR2108PBF	IR2136JPBF	IRF2804PBF
IPW90R1K2C3	IR2108SPBF	IR2136PBF	IRF2804SPBF
IPW90R340C3	IR21094PBF	IR2136SPBF	IRF2804STRLPBF
IPW90R500C3	IR21094SPBF	IR2181PBF	IRF2804STRRPBF
IPW90R800C3	IR2109PBF	IR2181SPBF	IRF2903ZSPBF
IPZ65R019C7	IR2109SPBF	IR2183PBF	IRF2903ZSTRLP
IPZ65R045C7	IR2110PBF	IR2183SPBF	IRF3205
IPZ65R065C7	IR2110SPBF	IR2184PBF	IRF3205S
IPZ65R095C7	IR2112PBF	IR2184SPBF	IRF3704ZSPBF
IR2010PBF	IR2112SPBF	IR2301PBF	IRF3707ZSPBF
IR2010S	IR2113PBF	IR2301SPBF	IRF3709ZSTRRPBF
IR2010SPBF	IR2113SPBF	IR2302PBF	IRF3710
IR2011PBF	IR2117PBF	IR2302SPBF	IRF3710S
IR2101PBF	IR2117SPBF	IRF1010N	IRF3805S-7PPBF
IR2101SPBF	IR2118PBF	IRF1010NS	IRF3805STRL-7PP
IR2102PBF	IR2118SPBF	IRF1010ZPBF	IRF4104PBF
IR2102SPBF	IR2127PBF	IRF1010ZSPBF	IRF510
IR2103PBF	IR2127SPBF	IRF1010ZSTRLPBF	IRF520
IR2103SPBF	IR2128PBF	IRF1010ZSTRRPBF	IRF520N
IR2104PBF	IR2128SPBF	IRF1310	IRF520NS
IR2104SPBF	IR21363JPBF	IRF1324S-7PPBF	IRF5210

Multisim 14.0 Full Components

IRF5210S	IRF6712STRPBF	IRF7748L1TRPBF	IRF8734TRPBF
IRF5305	IRF6713STRPBF	IRF7749L1TRPBF	IRF8736PBF
IRF5305S	IRF6714MTRPBF	IRF7759L2TRPBF	IRF8736TRPBF
IRF530N	IRF6715MTRPBF	IRF7769L1TRPBF	IRF8788PBF
IRF530NS	IRF6716MTRPBF	IRF7779L2TRPBF	IRF8788TRPBF
IRF540	IRF6717MTRPBF	IRF7799L2TRPBF	IRF9310PBF
IRF540N	IRF6718L2TRPBF	IRF7815PBF	IRF9310TRPBF
IRF540NS	IRF6727MTRPBF	IRF7815TRPBF	IRF9317PBF
IRF541	IRF6775MTRPBF	IRF7855PBF	IRF9317TRPBF
IRF6201PBF	IRF6785MTRPBF	IRF7855TRPBF	IRF9321PBF
IRF6201TRPBF	IRF6795MTRPBF	IRF7907PBF	IRF9321TRPBF
IRF6613TRPBF	IRF6797MTRPBF	IRF7907TRPBF	IRF9328PBF
IRF6614TRPBF	IRF6798MTRPBF	IRF7946TRPBF	IRF9328TRPBF
IRF6616TRPBF	IRF6810STRPBF	IRF830	IRF9333PBF
IRF6641TRPBF	IRF6811STRPBF	IRF8302MTRPBF	IRF9333TRPBF
IRF6643TRPBF	IRF6893MTRPBF	IRF8327STRPBF	IRF9335PBF
IRF6644TRPBF	IRF6894MTRPBF	IRF840	IRF9335TRPBF
IRF6645TRPBF	IRF6898MTRPBF	IRF8513TRPBF	IRF9362PBF
IRF6646TRPBF	IRF7201	IRF8707PBF	IRF9362TRPBF
IRF6648TRPBF	IRF7403	IRF8707TRPBF	IRF9383MTRPBF
IRF6655TRPBF	IRF7404	IRF8714PBF	IRF9389PBF
IRF6668TRPBF	IRF7413	IRF8714TRPBF	IRF9389TRPBF
IRF6674TRPBF	IRF7495PBF	IRF8721PBF	IRF9395MTRPBF
IRF6710S2TRPBF	IRF7495TRPBF	IRF8721TRPBF	IRF9530
IRF6711STRPBF	IRF7739L1TRPBF	IRF8734PBF	IRFB3004PBF

Multisim 14.0 Full Components

IRFB3006PBF	IRFB7446PBF	IRFH5206TRPBF	IRFHM831TRPBF
IRFB3077PBF	IRFB7530PBF	IRFH5207TRPBF	IRFHM8326TRPBF
IRFB3206PBF	IRFB7534PBF	IRFH5210TRPBF	IRFHM8330TRPBF
IRFB3207ZPBF	IRFB7537PBF	IRFH5215TRPBF	IRFHM8334TRPBF
IRFB3256PBF	IRFB7540PBF	IRFH5301TRPBF	IRFHM8337TRPBF
IRFB3306PBF	IRFB7545PBF	IRFH5302TRPBF	IRFHM8363TRPBF
IRFB3307ZPBF	IRFB7546PBF	IRFH5304TRPBF	IRFHM9391TRPBF
IRFB4020PBF	IRFE130	IRFH5406TRPBF	IRFHS8242TRPBF
IRFB4110PBF	IRFF110	IRFH6200TRPBF	IRFHS8342TRPBF
IRFB4115PBF	IRFG110	IRFH7107TRPBF	IRFHS9301TRPBF
IRFB4137PBF	IRFH4201TRPBF	IRFH7185TRPBF	IRFHS9351TRPBF
IRFB4227PBF	IRFH4210DTRPBF	IRFH8201TRPBF	IRFI1010N
IRFB4229PBF	IRFH4210TRPBF	IRFH8318TRPBF	IRFI3306GPBF
IRFB4310ZPBF	IRFH4213DTRPBF	IRFH8324TRPBF	IRFI3710
IRFB4321PBF	IRFH4213TRPBF	IRFH8325TRPBF	IRFI4410ZPBF
IRFB4332PBF	IRFH4234TRPBF	IRFH8330TRPBF	IRFI520N
IRFB4610PBF	IRFH4251DTRPBF	IRFH8334TRPBF	IRFI5210
IRFB4615PBF	IRFH4253DTRPBF	IRFH8337TRPBF	IRFI5305
IRFB4620PBF	IRFH5006TRPBF	IRFHM4226TRPBF	IRFI530N
IRFB5615PBF	IRFH5010TRPBF	IRFHM4231TRPBF	IRFI540N
IRFB5620PBF	IRFH5020TRPBF	IRFHM4234TRPBF	IRFI7536GPBF
IRFB7430PBF	IRFH5025TRPBF	IRFHM792TRPBF	IRFI840G
IRFB7434PBF	IRFH5106TRPBF	IRFHM8235TRPBF	IRFI840GLC
IRFB7437PBF	IRFH5110TRPBF	IRFHM830DTRPBF	IRFIZ44N
IRFB7440PBF	IRFH5204TRPBF	IRFHM830TRPBF	IRFIZ46N

Multisim 14.0 Full Components

IRFIZ48N	IRFP4768PBF	IRFR825PBF	IRFS4127PBF
IRFM140	IRFP5210	IRFR825TRPBF	IRFS4127TRLPBF
IRFM150	IRFP7430PBF	IRFS3004-7PPBF	IRFS4227PBF
IRFM9140	IRFP7530PBF	IRFS3004PBF	IRFS4227TRLPBF
IRFML8244TRPBF	IRFP7537PBF	IRFS3004TRL7PP	IRFS4321-7PPBF
IRFN054	IRFPG40	IRFS3004TRLPBF	IRFS4321TRL7PP
IRFP044N	IRFR110	IRFS3006-7PPBF	IRFS7430-7PPBF
IRFP048N	IRFR1205	IRFS3006TRL7PP	IRFS7430PBF
IRFP054N	IRFR120N	IRFS3107-7PPBF	IRFS7430TRL7PP
IRFP064	IRFR120ZPBF	IRFS3107TRL7PP	IRFS7430TRLPBF
IRFP064N	IRFR120ZTRPBF	IRFS3206PBF	IRFS7434-7PPBF
IRFP140N	IRFR2307ZPBF	IRFS3206TRRPBF	IRFS7434PBF
IRFP2410	IRFR2307ZTRLPBF	IRFS3207ZPBF	IRFS7434TRL7PP
IRFP244	IRFR2607ZPBF	IRFS3306PBF	IRFS7434TRLPBF
IRFP250	IRFR2607ZTRPBF	IRFS3306TRLPBF	IRFS7530PBF
IRFP260	IRFR3704ZPBF	IRFS3307ZPBF	IRFS7530TRLPBF
IRFP264	IRFR3704ZTRLPBF	IRFS3307ZTRLPBF	IRFS7534PBF
IRFP2907ZPBF	IRFR3704ZTRPBF	IRFS3307ZTRRPBF	IRFS7534TRLPBF
IRFP3006PBF	IRFR3910	IRFS4010-7PPBF	IRFS7537PBF
IRFP3710	IRFR4105	IRFS4010PBF	IRFS7537TRLPBF
IRFP4332PBF	IRFR4105ZPBF	IRFS4010TRL7PP	IRFS7540PBF
IRFP4368PBF	IRFR4105ZTRPBF	IRFS4010TRLPBF	IRFS7540TRLPBF
IRFP4468PBF	IRFR48ZPBF	IRFS4010TRRPBF	IRFSL3004PBF
IRFP4568PBF	IRFR48ZTRLPBF	IRFS4115PBF	IRFSL4115PBF
IRFP4668PBF	IRFR48ZTRPBF	IRFS4115TRLPBF	IRFSL7430PBF

Multisim 14.0 Full Components

IRFSL7530PBF	IRG4BC10UD	IRG4PC30KPBF	IRG4PSC71UPBF
IRFSL7534PBF	IRG4BC10UDPBF	IRG4PC30U	IRG4RC10K
IRFSL7537PBF	IRG4BC15UD	IRG4PC30UDPBF	IRG4RC10KD
IRFSL7540PBF	IRG4BC15UDPBF	IRG4PC30UPBF	IRG4RC10U
IRFU110	IRG4BC20FDPBF	IRG4PC40FPBF	IRG4RC10UD
IRFU1205	IRG4BC20SDPBF	IRG4PC40SPBF	IRG4RC10UDPBF
IRFU120N	IRG4BC20SD-SPBF	IRG4PC40UD-EPBF	IRG4RC10UDTRLP
IRFU2605	IRG4BC20U	IRG4PC40UDPBF	IRG4RC10UDTRP
IRFU3710ZPBF	IRG4BC20UDPBF	IRG4PC40UPBF	IRG4RC10UDTRRP
IRFU3910	IRG4BC20UPBF	IRG4PC50FD-EPBF	IRG4RC10UTRPBF
IRFU4105	IRG4BC30FPBF	IRG4PC50FDPBF	IRG4RC20FPBF
IRFU4105ZPBF	IRG4BC30KDPBF	IRG4PC50KDPBF	IRG4RC20FTRLPBF
IRFU48ZPBF	IRG4BC30UDPBF	IRG4PC50KPBF	IRG4RC20FTRPBF
IRFZ24N	IRG4BC30UPBF	IRG4PC50SPBF	IRG7PH46UD-EP
IRFZ24NS	IRG4BC40S	IRG4PC50UD-EPBF	IRG7PH46UDPBF
IRFZ34N	IRG4BC40SPBF	IRG4PC50UDPBF	IRG7PH46U-EP
IRFZ44N	IRG4BC40U	IRG4PC50UPBF	IRG7PH46UPBF
IRFZ44NS	IRG4BC40UPBF	IRG4PC50WPBF	IRG7PSH73K10PBF
IRFZ46N	IRG4BC40W	IRG4PF50WPBF	IRGB15B60KDPBF
IRFZ46NS	IRG4BC40WPBF	IRG4PH20KPBF	IRGB20B60PD1PBF
IRFZ48N	IRG4MC30F	IRG4PH50SPBF	IRGB30B60KPBF
IRFZ48NS	IRG4MC40U	IRG4PH50UDPBF	IRGB4045DPBF
IRFZ48ZSPBF	IRG4MC50F	IRG4PH50UPBF	IRGB4059DPBF
IRG4BC10KDPBF	IRG4MC50U	IRG4PSC71KDPBF	IRGB4060DPBF
IRG4BC10U	IRG4PC30KDPBF	IRG4PSC71KPBF	IRGB4061DPBF

Multisim 14.0 Full Components

IRGB4062DPBF	IRGPC40UD2	IRL2910S	IRLH5034TRPBF
IRGB4B60KD1PBF	IRGPC50K	IRL3103	IRLH5036TRPBF
IRGB5B120KDPBF	IRGPC50M	IRL3103S	IRLHM620TRPBF
IRGB8B60KPBF	IRGPH40K	IRL3303	IRLHS2242TRPBF
IRGBC20F	IRGPH50K	IRL3303S	IRLHS6242TRPBF
IRGBC20K	IRGPH50M	IRL3705	IRLHS6276TRPBF
IRGBC20S	IRGPS40B120UDP	IRL3705N	IRLHS6342TRPBF
IRGBC20U	IRGPS60B120KDP	IRL3705NS	IRLHS6376TRPBF
IRGBC30F	IRGS15B60KDPBF	IRL3803	IRLI2203G
IRGBC30K	IRGS30B60KPBF	IRL3803S	IRLI2203N
IRGBC30UD2	IRGS4B60KD1PBF	IRL530N	IRLI2505
IRGLC60KD1	IRGS8B60KPBF	IRL530NS	IRLI2703
IRGP20B120UD-EP	IRGS8B60KTRLPBF	IRL540	IRLI2910
IRGP30B120KD-EP	IRGSL15B60KDPBF	IRL6283MTRPBF	IRLI3103
IRGP30B60KD-EP	IRGSL30B60KPBF	IRL6297SDTRPBF	IRLI3303
IRGP4062D-EPBF	IRGSL4B60KD1PBF	IRL6342PBF	IRLI3803
IRGP4062DPBF	IRL1404ZPBF	IRL6342TRPBF	IRLI530N
IRGP4063D-EPBF	IRL2203	IRL7833SPBF	IRLIZ24N
IRGP4063DPBF	IRL2203NS	IRL7833STRLPBF	IRLIZ34N
IRGP4068D-EPBF	IRL2203S	IRL8113PBF	IRLL3303
IRGP4068DPBF	IRL2505	IRL8113SPBF	IRLML0030TRPBF
IRGP50B60PD1PBF	IRL2505S	IRL8113STRLPBF	IRLML0040TRPBF
IRGPC20F	IRL2703	IRLB3034PBF	IRLML0060TRPBF
IRGPC20U	IRL2703S	IRLB3036PBF	IRLML0100TRPBF
IRGPC40K	IRL2910	IRLB8748PBF	IRLML2030TRPBF

Multisim 14.0 Full Components

IRLML2060TRPBF	IRLR3636PBF	IRLS4030TRL7PP	J175
IRLML2244TRPBF	IRLR3636TRLPBF	IRLS4030TRLPBF	J176
IRLML6244TRPBF	IRLR3636TRPBF	IRLSL4030PBF	J177
IRLML6246TRPBF	IRLR3705ZPBF	IRLTS2242TRPBF	J210
IRLML6346TRPBF	IRLR3705ZTRPBF	IRLU024N	J211
IRLML9301TRPBF	IRLR3717PBF	IRLU2703	J212
IRLML9303TRPBF	IRLR3717TRPBF	IRLU2705	J2N5902
IRLP150	IRLR3717TRRPBF	IRLU2905	J2N5904
IRLP2203	IRLR6225PBF	IRLU2905ZPBF	J2N5905
IRLP2505	IRLR6225TRPBF	IRLU3103	J2N5906
IRLP3705	IRLR7807ZPBF	IRLU3110ZPBF	J2N5907
IRLP3803	IRLR7807ZTRPBF	IRLU3303	J2N5908
IRLR024N	IRLR8256PBF	IRLU3636PBF	J2N5909
IRLR2703	IRLR8256TRPBF	IRLU3705ZPBF	J2N5911
IRLR2705	IRLR8726PBF	IRLU8743PBF	J2N5912
IRLR2905	IRLR8726TRLPBF	IRLZ34N	J2N6483
IRLR2905ZPBF	IRLR8726TRPBF	IRLZ34NS	J2N6484
IRLR2905ZTRLPBF	IRLR8729PBF	IRLZ44N	J2N6485
IRLR2905ZTRPBF	IRLR8729TRLPBF	J108	J308
IRLR3103	IRLR8729TRPBF	J109	J309
IRLR3110ZPBF	IRLR8743PBF	J110	J310
IRLR3110ZTRLPBF	IRLR8743TRLPBF	J111	J401
IRLR3110ZTRPBF	IRLR8743TRPBF	J112	J402
IRLR3110ZTRRPBF	IRLS4030-7PPBF	J113	J403
IRLR3303	IRLS4030PBF	J174	J404

Multisim 14.0 Full Components

J405	L6205_DIP20	L6911C_SO20	LCD_DISPLAY_24x2
J406	L6205_SO20	L6911D_SO20	LCD_DISPLAY_30x2
J410	L6206_DIP24	L6911E_SO20	LCD_DISPLAY_32x2
J411	L6206_SO24	LA_CARRY_GEN	LCD_DISPLAY_40x2
J412	L6206P_SO36	LA_CARRY_GEN	LCD_DISPLAY_4DIGI T
JAN2N2907A	L6207_DIP24	LAMP	LD102A
JAN2N3700	L6207_SO24	LAMP_VIRTUAL	LD103A
JAN2N4029	L6207P_SO36	LATCH_D	LD106
JAN2N4033	L6208_DIP24	LATCH_D2	LED
JANTX2N2907A	L6208_SO24	LATCH_D4_SR_OE	LED_blue
JANTX2N3700	L6208P_SO36	LATCH_SR	LED_BLUE_RATED
JANTX2N4029	L6234_DIP20	LATTICE- ispDOWNLOAD- HDR	LED_green
JANTX2N4033	L6234P_SO20		LED_GREEN_RATED
JANTXV2N2907A	L6375_DIP8	LATTICE- ispDOWNLOAD- USB-HDR	LED_ir
JANTXV2N3700	L6375_SO20		LED_orange
JANTXV2N4029	L64210GC-15	LC03-6R2G	LED_red
JANTXV2N4033	L64210GC-20	LCD_DISPLAY_08x1	LED_RED_RATED
JFET_N	L64210JC-15	LCD_DISPLAY_08x2	LED_yellow
JFET_P	L64210JC-20	LCD_DISPLAY_10x2	LED_YELLOW_RATE D
JK_FF	L64210NC-15	LCD_DISPLAY_16x1	LF13741H
JK_FF_NEGSR	L64210NC-20	LCD_DISPLAY_16x2	LF147D/883
L6201_SO20	L64211GC-15	LCD_DISPLAY_16x4	LF147J
L6201P_SO20	L64211GC-20	LCD_DISPLAY_20x2	LF147J/883
L6202_DIP18	L64211NC-15	LCD_DISPLAY_20x4	LF155AH
L6203_ZIP11	L64211NC-20		

Multisim 14.0 Full Components

LF155AH/883	LF353P	LF411CN	LF442ACN
LF155H	LF355AH	LF411CP	LF442AMH
LF155H/883	LF355BM	LF411ID	LF442CD
LF156AH	LF355BN	LF411IP	LF442CH
LF156AH/883	LF355H	LF411MH	LF442CJ
LF156H	LF355M	LF411MH/883	LF442CM
LF156H/883	LF355N	LF411MWG/883	LF442CN
LF157AH/883	LF356AH	LF412ACH	LF442MH
LF157H/883	LF356BM	LF412ACN	LF442MH/883
LF255H	LF356BN	LF412AMH	LF444ACN
LF256H	LF356H	LF412CD	LF444AMD
LF257H	LF356M	LF412CH	LF444CD
LF347BD	LF356N	LF412CJG	LF444CJ
LF347BN	LF357AH	LF412CN	LF444CM
LF347D	LF357BN	LF412CP	LF444CN
LF347M	LF357H	LF412MH	LF444MD/883
LF347N	LF357M	LF412MH/883	LF451CM
LF351D	LF357N	LF412MJ/883	LF453CM
LF351M	LF400	LF441AMH	LH0003CH
LF351N	LF411ACH	LF441CD	LH0003H
LF351P	LF411ACN	LF441CH	LH0004CH
LF353D	LF411AMH	LF441CJ	LH0004H
LF353H	LF411CD	LF441CM	LH0004H-MIL
LF353M	LF411CH	LF441CN	LH0021CK
LF353N	LF411CJG	LF441MH/883	LH0021K

Multisim 14.0 Full Components

LH0022CD	LH4161	LM101AW	LM108D
LH0022CH	LH4162	LM101AW/883	LM108D/883
LH0024CH	LHV870LC/NOPB	LM101D	LM108H
LH0024H	LIMIT_NC	LM101F	LM108H/883
LH0024H-MIL	LIMIT_NO	LM101F/883	LM108J
LH0032CG	LINKSYS-WRT54G- HD	LM101H	LM108J/883
LH0032G	LM101AD	LM101H/883	LM108J8
LH0032G/883	LM101AD/883	LM101J-14	LM108J-8
LH0041CG	LM101AF	LM101J-14/883	LM108J8/883
LH0041CJ	LM101AF/883	LM107J	LM108J-8/883
LH0041G	LM101AFK	LM107JG	LM108JG
LH0042CH	LM101AFK/883	LM107JG/883	LM108JG/883
LH0042H	LM101AH	LM107U	LM108L
LH0042H-MIL	LM101AH/883	LM107W	LM108P
LH0062CD	LM101AJ	LM107W/883	LM10BH
LH0062CH	LM101AJ/883	LM108AD	LM10BLH
LH0062D	LM101AJ-14	LM108AH	LM10CH
LH0062H	LM101AJ-14/883	LM108AH/883	LM10CLH
LH0101ACK	LM101AJ8	LM108AJ	LM10CLN
LH0101AK	LM101AJG	LM108AJ/883	LM10CLN8
LH0101AK-MIL	LM101AJG/883	LM108AJ-8	LM10CLWM
LH0101CK	LM101AP	LM108AJ-8/883	LM10CN
LH0101K	LM101AU	LM108AJG	LM10CN8
LH0101K-MIL	LM101AU/883	LM108AL	LM10CWM
LH1041G		LM108AP	LM10H

Multisim 14.0 Full Components

LM10H/883	LM11CLH	LM13700N	LM158JG
LM111E	LM11CLN	LM139AJ	LM158N
LM111E/883	LM11H	LM139AW	LM158P
LM111H	LM124AD	LM139E	LM160H
LM111J-14	LM124AE	LM139J	LM160J
LM111J-8	LM124AE/883	LM139W	LM160J-14
LM111W	LM124AFK	LM144H	LM1877M-9
LM112H	LM124AJ	LM144H/883	LM1877N-9
LM112H/883	LM124AJ/883	LM146J	LM202H
LM117HVH	LM124AN	LM146J/883	LM207D
LM117HVKSTL/883	LM124AW/883	LM149J	LM207H
LM118D	LM124AWG/883	LM149J/883	LM207J
LM118FK	LM124D	LM158AD	LM207P
LM118H	LM124E	LM158AFK	LM208AD
LM118H/883	LM124E/883	LM158AH	LM208AH
LM118J	LM124FK	LM158AH/883	LM208AJ
LM118J/883	LM124J	LM158AJ	LM208AJ-8
LM118J8	LM124J/883	LM158AJG	LM208AN
LM118J-8	LM124N	LM158AN	LM208AP
LM118J8/883	LM124W	LM158AP	LM208D
LM118J-8/883	LM124W/883	LM158AWG/883	LM208H
LM118JG	LM12CLK	LM158D	LM208J
LM118L	LM12LK	LM158FK	LM208J-8
LM118P	LM13700AN	LM158H	LM208N
LM11CH	LM13700M	LM158J	LM208P

Multisim 14.0 Full Components

LM211H	LM224N	LM2900N	LM2903DR2
LM211J-8	LM224NG	LM2901DG	LM2903DR2G
LM211M	LM224P	LM2901DR2G	LM2903NG
LM212H	LM239AJ	LM2901DTBR2G	LM2904ADMR2G
LM216AD	LM239DG	LM2901NG	LM2904AN
LM216AF	LM239DR2G	LM2901VDG	LM2904ANG
LM216AH	LM239DTBR2G	LM2901VDR2G	LM2904D
LM216D	LM239J	LM2901VDTBR2G	LM2904DG
LM216F	LM239NG	LM2901VNG	LM2904DMR2G
LM216H	LM246J	LM2902DG	LM2904DR2G
LM218D	LM258AD	LM2902DR2G	LM2904ITP
LM218H	LM258AH	LM2902DTBG	LM2904M
LM218JG	LM258AJG	LM2902DTBR2G	LM2904N
LM218P	LM258AN	LM2902M	LM2904NG
LM221H	LM258AP	LM2902MT	LM2904P
LM224AD	LM258D	LM2902N	LM2904PW
LM224AJ	LM258DG	LM2902NG	LM2904QD
LM224AN	LM258DMR2G	LM2902VD	LM2904QP
LM224AP	LM258DR2G	LM2902VDG	LM2904VD
LM224D	LM258H	LM2902VDR2G	LM2904VDG
LM224DG	LM258JG	LM2902VDTBG	LM2904VDMR2G
LM224DR2G	LM258N	LM2902VDTBR2G	LM2904VDR2G
LM224DTBG	LM258NG	LM2902VN	LM2904VN
LM224DTBR2G	LM258P	LM2903DG	LM2904VNG
LM224J	LM2878P	LM2903DMR2G	LM2924M

Multisim 14.0 Full Components

LM2924N	LM311H	LM324AP	LM339M
LM293D	LM311M	LM324APWLE	LM339N
LM293DG	LM311N	LM324D	LM339NG
LM293DMR2G	LM311N-14	LM324DBLE	LM344H
LM293DR2G	LM312H	LM324DG	LM346J
LM301AD	LM318D	LM324DR2G	LM346M
LM301AJ8	LM318H	LM324DTBG	LM346N
LM301AP	LM318J8	LM324DTBR2G	LM348D
LM3046M	LM318J-8	LM324J	LM348N
LM307D	LM318M	LM324M	LM348PW
LM307N	LM318N	LM324MT	LM358AD
LM307P	LM318N8	LM324N	LM358ADR2G
LM308AD	LM318P	LM324NG	LM358AH
LM308AH	LM318S8	LM324P	LM358AJG
LM308AJ	LM321AH	LM324PWLE	LM358AM
LM308AJ-8	LM321H	LM324x2DBLE	LM358AN
LM308AN	LM324AD	LM3301N	LM358AP
LM308AN8	LM324ADG	LM3302N	LM358BP
LM308D	LM324ADR2G	LM339AJ	LM358D
LM308H	LM324ADTBG	LM339AM	LM358DB
LM308J	LM324ADTBR2G	LM339AN	LM358DG
LM308J-8	LM324AJ	LM339DG	LM358DMR2G
LM308M	LM324AM	LM339DR2G	LM358DR2G
LM308N	LM324AN	LM339DTBR2G	LM358H
LM308N8	LM324ANG	LM339J	LM358J

Multisim 14.0 Full Components

LM358JG	LM4871LD	LM6142BIM	LM6171BIM
LM358M	LM4871M	LM6142BIN	LM6171BIN
LM358N	LM4871MM/NOPB	LM6152ACM	LM6172AMJFQML
LM358NG	LM4871MX	LM6152BCM	LM6172AMWGFQ ML
LM358P	LM555CM	LM6161E/883	LM6172IM
LM358PW	LM555CN	LM6161J	LM6172IN
LM358TP	LM556CM	LM6161J/883	LM6181IM
LM359J	LM556CN	LM6161W/883	LM6181IN
LM359M	LM607ACH	LM6161WG/883	LM6211MF
LM359N	LM607ACN	LM6162E/883	LM6218AN
LM3875TF/NOPB	LM607AMH	LM6162J/883	LM6218AWM
LM3900D	LM607BCH	LM6162N	LM6218N
LM3900M	LM607BCN	LM6162W/883	LM6218WM
LM3900N	LM607BMH	LM6162WG/883	LM6261J
LM393DG	LM607CH	LM6164E/883	LM6261M
LM393DMR2G	LM607CN	LM6164J	LM6261N
LM393DR2G	LM6118E/883	LM6164J/883	LM6262M
LM393NG	LM6118J/883	LM6164W/883	LM6262N
LM4250CH	LM6118N	LM6164WG/883	LM6264J
LM4250CM	LM6132AIM	LM6165E/883	LM6264N
LM4250CN	LM6132BIM	LM6165J	LM6265J
LM4250J-MIL	LM6132BIN	LM6165J/883	LM6265N
LM4562HA	LM6142AIM	LM6165W/883	LM627ACH
LM4562MA	LM6142AIN	LM6165WG/883	LM627AMH
LM4562NA	LM6142AMJ-MLS	LM6171AIM	

Multisim 14.0 Full Components

LM627BCH	LM710AMJ	LM725H	LM741J-14/883
LM627BMH	LM710AMW	LM725H/883	LM741W/883
LM627CH	LM710CH	LM7301IM	LM747AH
LM627CN	LM710CN	LM7301IM5	LM747AJ
LM6313N	LM710H	LM7321MA	LM748CH
LM6361J	LM7121IM	LM7321MF	LM748CJ
LM6361M	LM7121IM5	LM7322MA	LM748CN
LM6361N	LM7131ACM	LM7322MM	LM748H
LM6362M	LM7131ACM5	LM7332MA	LM759CH
LM6362N	LM715CH	LM7332MM	LM759CP
LM6364M	LM715CJ	LM7341MF	LM759H/883
LM6364N	LM715MH	LM7372IMA	LM759MH
LM6365M	LM715MJ	LM7372MR	LM7805CT
LM6365N	LM7171AIM	LM741AH/883	LM7809CT
LM637ACH	LM7171AIN	LM741AJ-14/883	LM7812CT
LM637AMH	LM7171AMJFQML	LM741CH	LM7815CT
LM637BCH	LM7171BIM	LM741CJ	LM7818CT
LM637BMH	LM7171BIN	LM741CM	LM7824CT
LM637CH	LM723CN	LM741CN	LM7905CT
LM637CN	LM723E	LM741EH	LM7909CT
LM709AH	LM723H	LM741EN	LM7912CT
LM709CH	LM725AH	LM741H	LM7915CT
LM709CN	LM725AH/883	LM741H/883	LM7918CT
LM709CN-8	LM725CH	LM741J	LM7924CT
LM709H	LM725CN	LM741J/883	LM8261M5

Multisim 14.0 Full Components

LM8272MM	LMC6042AIM	LMC6081AMN	LMC6482IM
LM833D	LMC6042AIN	LMC6081IM	LMC6482IMM
LM833DG	LMC6042IM	LMC6081IN	LMC6482IN
LM833DR2G	LMC6042IN	LMC6082AIM	LMC6482MN
LM833NG	LMC6044AIM	LMC6082AIN	LMC6484AIM
LMC555CH	LMC6044AIN	LMC6082AMN	LMC6484AIN
LMC555CM	LMC6044IM	LMC6082IM	LMC6484AMJ/883
LMC555CN	LMC6044IN	LMC6082IN	LMC6484AMWG/883
LMC6001AIN	LMC6061AIM	LMC6084AIM	LMC6484IM
LMC6001BIN	LMC6061AIN	LMC6084IM	LMC6484IN
LMC6022IM	LMC6061AMJ/883	LMC6442AIM	LMC6484MN
LMC6024IM	LMC6061AMN	LMC6442IM	LMC6492AEM
LMC6032IM	LMC6061IM	LMC6442IN	LMC6492BEM
LMC6032IN	LMC6061IN	LMC6462AIM	LMC6494AEM
LMC6034IM	LMC6062AIM	LMC6462AIN	LMC6494BEM
LMC6035IBP	LMC6062AIN	LMC6462BIM	LMC6572AIM
LMC6035IM	LMC6062AMJ/883	LMC6462BIN	LMC6572BIM
LMC6035IMM	LMC6062AMN	LMC6464AIM	LMC6574AIM
LMC6035ITL	LMC6062IM	LMC6464AMWG-QML	LMC6574BIM
LMC6036IM	LMC6062IN	LMC6464BIM	LMC660AIM
LMC6036IMT	LMC6064AIM	LMC6464BIN	LMC660AIN
LMC6041AIM	LMC6064IM	LMC6482AIM	LMC660AMD
LMC6041AIN	LMC6064IN	LMC6482AIN	LMC660AMJ/883
LMC6041IM	LMC6081AIM	LMC6482AMJ/883	LMC660CM
LMC6041IN	LMC6081AIN		

Multisim 14.0 Full Components

LMC660CN	LMC7221BIM5	LMH6503MA	LMH6622MM
LMC662AIM	LMC7225IM5	LMH6503MT	LMH6624J-QML
LMC662AIN	LMC8101BP	LMH6505MA	LMH6624MA
LMC662AMD	LMC8101MM	LMH6505MM	LMH6624MF
LMC662AMJ/883	LMC8101TP	LMH6521SQ/NOPB	LMH6628JFQML
LMC662CM	LME49600TS/NOPB	LMH6550MA	LMH6628MA
LMC662CN	LME49710HA	LMH6550MM	LMH6628WGFQML
LMC6762AIM	LME49710MA	LMH6551MA	LMH6629MF
LMC6762BIM	LME49710NA	LMH6551MM	LMH6629SD
LMC6772AIM	LME49713HA/NOP B	LMH6552MA	LMH6639MA
LMC6772AIMM	LME49713MA/NOP B	LMH6552SD	LMH6639MF
LMC6772BIM	LME49720HA	LMH6553MR	LMH6642MA
LMC6772BIN	LME49720MA	LMH6553SD	LMH6642MF
LMC7101AIM5	LME49720NA	LMH6554LE	LMH6642MFXEP
LMC7101BIM5	LME49720NA	LMH6555SQ	LMH6643MA
LMC7111BIM5	LME49721MA/NOP B	LMH6559MA	LMH6643MAXEP
LMC7211AIM	LME49740MA	LMH6559MF	LMH6643MM
LMC7211AIM5	LME49740NA	LMH6601MG	LMH6644MA
LMC7211BIM	LME49990MA/NOP B	LMH6609MA	LMH6644MAXEP
LMC7211BIM5	LMH6321MR	LMH6609MF	LMH6644MT
LMC7215IM	LMH6321TS	LMH6611MK	LMH6645MA
LMC7215IM5	LMH6502MA	LMH6612MA	LMH6645MF
LMC7221AIM	LMH6502MT	LMH6618MK	LMH6646MA
LMC7221AIM5		LMH6619MA	LMH6646MM
LMC7221BIM		LMH6622MA	LMH6647MA

Multisim 14.0 Full Components

LMH6647MF	LMH6723MF	LMP2234BMT	LMP8271MA
LMH6655MA	LMH6733MQ	LMP7300MA	LMP8272MA
LMH6655MM	LMH6738MQ	LMP7300MM	LMP8275MA
LMH6657MF	LMH6739MQ	LMP7701MA	LMP8276MA
LMH6657MG	LMP2011MA	LMP7701MF	LMP8277MA
LMH6672MA	LMP2011MF	LMP7702MA	LMP8601MA
LMH6672MR	LMP2015MA	LMP7702MM	LMP8601QMA
LMH6702J-QML	LMP2015MF	LMP7704MA	LMP8602MA
LMH6702MA	LMP2016MA	LMP7704MT	LMP8602MM
LMH6702MF	LMP2016MM	LMP7707MF	LMP8602QMA
LMH6703MA	LMP2021MA	LMP7708MM	LMP8602QMM
LMH6703MF	LMP2021MF	LMP7709MT	LMP8603MA
LMH6714J-QML	LMP2022MA	LMP7711MK	LMP8603MM
LMH6714MA	LMP2022MM	LMP7712MM	LMP8603QMA
LMH6714MF	LMP2231AMA	LMP7715MF	LMP8603QMM
LMH6715JFQML	LMP2231AMF	LMP7716MM	LMP8645HVMMK
LMH6715MA	LMP2231BMA	LMP7717MA	LMP8645MK
LMH6718MA	LMP2231BMF	LMP7717MF	LMP8671MA/NOPB
LMH6720J-QML	LMP2232AMA	LMP7718MA	LMP8672MA/NOPB
LMH6720MA	LMP2232AMM	LMP7718MM	LMP8674MA/NOPB
LMH6720MF	LMP2232BMA	LMP7731MA	LMV2011MA
LMH6722J-QML	LMP2232BMM	LMP7731MF	LMV2011MF
LMH6722MA	LMP2234AMA	LMP7732MA	LMV321M5
LMH6722MT	LMP2234AMT	LMP7732MM	LMV321M7
LMH6723MA	LMP2234BMA	LMP8270MA	LMV324M

Multisim 14.0 Full Components

LMV324MT	LMV641MA	LMV793MF	LMV931MF
LMV331M5	LMV641MG	LMV794MA	LMV931MG
LMV331M7	LMV651MG	LMV794MM	LMV932MA
LMV339M	LMV652MM	LMV796MF	LMV932MM
LMV339MT	LMV654MT	LMV797MM	LMV934MA
LMV342MA	LMV711M6	LMV821M5	LMV934MT
LMV342MM	LMV716MM	LMV821M7	LMV951MK
LMV358M	LMV7219M5	LMV822M	LMV981BL
LMV358MM	LMV7219M7	LMV822MM	LMV981MF
LMV393M	LMV721M5	LMV824M	LMV981MG
LMV393MM	LMV721M7	LMV824MT	LMV981TL
LMV551MG	LMV7271MF	LMV831MG	LMX321AUK+
LMV552MM	LMV7271MG	LMV832MM	LMX321AXK+
LMV554MT	LMV7291MG	LMV834MT	LMX324ASD+
LMV601MG/NOPB	LMV751M5	LMV841MG	LMX324AUD+
LMV602MA/NOPB	LMV761MA	LMV842MA	LMX358AKA+
LMV602MM/NOPB	LMV761MF	LMV842MM	LMX358ASA+
LMV604MA/NOPB	LMV771MG	LMV844MA	LMX358AUA+
LMV604MT/NOPB	LMV772MA	LMV844MT	LOG101AID
LMV611MF/NOPB	LMV772MM	LMV851MG	LOG102AID
LMV611MG/NOPB	LMV772QMM	LMV852MM	LOG104AID
LMV612MA/NOPB	LMV774MT	LMV854MT	LOG112AID
LMV612MM/NOPB	LMV791MK	LMV861MG	LOG114AIRGVR
LMV614MA/NOPB	LMV792MM	LMV862MM	LOSSLESS_LINE_TYP E1
LMV614MT/NOPB	LMV793MA	LMV881LE/NOPB	

Multisim 14.0 Full Components

LOSSLESS_LINE_TYP E2	LPC661AIM	LPR201PC15	LT1002CJ
	LPC661AIN	LPR201PC20	LT1002CN
LOSSY_TRANSMISSI ON_LINE	LPC661AMN	LPV321M5	LT1002MJ
LP124J	LPC661IM	LPV321M7	LT1006ACH
LP239D	LPC661IN	LPV324M	LT1006ACJ8
LP239J	LPC662AIM	LPV324MT	LT1006AMH
LP239N	LPC662AIN	LPV358MM	LT1006AMJ8
LP2901D	LPC662AMD	LPV358MX	LT1006CH
LP2901J	LPC662AMJ/883	LPV511MG	LT1006CJ8
LP2901N	LPC662IM	LPV521MG	LT1006CN8
LP2902M	LPC662IN	LT1001	LT1006MH
LP2902N	LPR200JC10	LT1001ACH	LT1006MJ8
LP311M	LPR200JC12	LT1001ACJ8	LT1006S8
LP311N	LPR200JC15	LT1001ACN8	LT1007ACH
LP324M	LPR200JC20	LT1001AMH/883	LT1007ACJ8
LP324N	LPR200PC10	LT1001AMJ8/883	LT1007ACN8
LP339D	LPR200PC12	LT1001CH	LT1007ACP
LP339J	LPR200PC15	LT1001CJ8	LT1007AMH
LP339M	LPR200PC20	LT1001CN8	LT1007AMJ8
LP339N	LPR201JC10	LT1001CS8	LT1007AMJG
LPC660AIM	LPR201JC12	LT1001MH	LT1007AML
LPC660AIN	LPR201JC15	LT1001MJ8	LT1007AMP
LPC660AMD	LPR201JC20	LT1002ACJ	LT1007CDW
LPC660AMJ/883	LPR201PC10	LT1002ACN	LT1007CH
LPC660IM	LPR201PC12	LT1002AMJ	LT1007CJ8

Multisim 14.0 Full Components

LT1007CN8	LT1012DH	LT1013MFK	LT1021BMH-10
LT1007CP	LT1012DN8	LT1013MH	LT1021DCS8-10
LT1007CS	LT1012MH	LT1013MJ8	LT1021DCS8-5
LT1007MH	LT1012S8	LT1013MJG	LT1021DCS8-7
LT1007MJ8	LT1013ACH	LT1013MP	LT1022ACH
LT1007MJG	LT1013ACJ8	LT1014ACJ	LT1022AMH
LT1007ML	LT1013ACP	LT1014AMJ	LT1022CH
LT1007MP	LT1013AIP	LT1014CJ	LT1022CN8
LT1008CH	LT1013AMFK	LT1014CN	LT1022MH
LT1008CN8	LT1013AMH	LT1014DN	LT1024ACN
LT1008MH	LT1013AMJ8	LT1014MJ	LT1024AMD
LT1008S8	LT1013AMP	LT1016CN8	LT1024CN
LT1010CDD	LT1013CH	LT1016CS8	LT1024MD
LT1010CH	LT1013CJ8	LT1016IN8	LT1028
LT1010CN8	LT1013CN8	LT1016IS8	LT1028ACH
LT1010CT	LT1013CP	LT1017CN8	LT1028ACJ8
LT1010MH	LT1013DD	LT1017CS8	LT1028ACN8
LT1011CN8	LT1013DID	LT1017CSW	LT1028AMH
LT1011CS8	LT1013DIP	LT1018CN8	LT1028AMJ8
LT1012	LT1013DMD	LT1018CS8	LT1028CH
LT1012ACH	LT1013DMJG	LT1018CSW	LT1028CJ8
LT1012ACN8	LT1013DMP	LT1021BCH-5	LT1028CN8
LT1012AMH	LT1013DN8	LT1021BCN8-10	LT1028CS
LT1012CH	LT1013DP	LT1021BCN8-5	LT1028MH
LT1012CN8	LT1013IP	LT1021BCN8-7	LT1028MJ8

Multisim 14.0 Full Components

LT1037ACH	LT1055S8	LT1077ACH	LT1079CN
LT1037ACJ8	LT1056ACH	LT1077ACJ8	LT1079IN
LT1037ACN8	LT1056AMH	LT1077ACN8	LT1079ISW
LT1037ACP	LT1056CH	LT1077AIN8	LT1079MJ
LT1037AMH	LT1056CN8	LT1077AMH	LT1079SW
LT1037AMJ8	LT1056MH	LT1077AMJ8	LT1083CP
LT1037AMJG	LT1056S8	LT1077CH	LT1084CP
LT1037AML	LT1057ACH	LT1077CJ8	LT1084CT
LT1037AMP	LT1057ACJ8	LT1077CN8	LT1085CM
LT1037CDW	LT1057ACN8	LT1077IN8	LT1085CT
LT1037CH	LT1057AMH	LT1077IS8	LT1097CN8
LT1037CJ8	LT1057AMJ8	LT1077MH	LT1097S8
LT1037CN8	LT1057CH	LT1077MJ8	LT1101ACH
LT1037CP	LT1057CJ8	LT1077S8	LT1101ACJ8
LT1037CS	LT1057CN8	LT1078ACH	LT1101ACN8
LT1037MH	LT1057IS	LT1078ACN8	LT1101AIN8
LT1037MJ8	LT1057MH	LT1078AMJ8	LT1101AMH
LT1037MJG	LT1057MJ8	LT1078CN8	LT1101AMJ8
LT1037ML	LT1057S	LT1078IN8	LT1101CH
LT1037MP	LT1058ACJ	LT1078IS8	LT1101CJ8
LT1055ACH	LT1058ACN	LT1078MH	LT1101CN8
LT1055AMH	LT1058AMJ	LT1078MJ8	LT1101IN8
LT1055CH	LT1058CJ	LT1078S8	LT1101MH
LT1055CN8	LT1058CMJ	LT1079ACN	LT1101MJ8
LT1055MH	LT1058CN	LT1079AM	LT1101S

Multisim 14.0 Full Components

LT1102ACN8	LT1122DMJ8	LT1178AMJ8	LT118AH
LT1102CN8	LT1122DS8	LT1178CH	LT118AJ8
LT1102IN8	LT1124CN8	LT1178CJ8	LT1190CJ8
LT1112S8	LT1124CS8	LT1178CN8	LT1190CN8
LT1113ACN8	LT1125CN	LT1178IN8	LT1190CS8
LT1113CS8	LT1125CSW	LT1178MH	LT1190MJ8
LT1114S	LT1126CN8	LT1178MJ8	LT1191CJ8
LT1115CN8	LT1126CS8	LT1178S	LT1191CN8
LT1115CS	LT1127CN	LT1179ACJ	LT1191CS8
LT1116CN8	LT1127CSW	LT1179ACN	LT1191MJ8
LT1116CS8	LT1128CN8	LT1179AMJ	LT1192CJ8
LT1121CN8	LT1128CS8	LT1179CJ	LT1192CN8
LT1121CS8	LT1129CQ	LT1179CN	LT1192CS8
LT1122ACJ8	LT1129CS8	LT1179IN	LT1192MJ8
LT1122ACN8	LT1129CT	LT1179MJ	LT1193CJ8
LT1122AMJ8	LT1167CN8	LT1179S	LT1193CN8
LT1122BCJ8	LT1167CS8	LT1179SW	LT1193CS8
LT1122BCN8	LT1168CN8	LT1187CJ8	LT1193MJ8
LT1122BMJ8	LT1168CS8	LT1187CN8	LT1194CJ8
LT1122CCJ8	LT1169CN8	LT1187CS8	LT1194CN8
LT1122CCN8	LT1169CS8	LT1187MJ8	LT1194CS8
LT1122CMJ8	LT1178ACH	LT1189CJ8	LT1194MJ8
LT1122CS8	LT1178ACJ8	LT1189CN8	LT1195CJ8
LT1122DCJ8	LT1178ACN8	LT1189CS8	LT1195CN8
LT1122DCN8	LT1178AMH	LT1189MJ8	LT1195CS8

Multisim 14.0 Full Components

LT1195MJ8	LT1213ACN8	LT1221MJ8	LT1230MJ
LT1200	LT1213AMJ8	LT1222CN8	LT1251CN
LT1201CN8	LT1213CN8	LT1222IS8	LT1251CS
LT1201CS8	LT1213CS8	LT1223CJ8	LT1252CN8
LT1202CN	LT1213MJ8	LT1223CN8	LT1252CS8
LT1202CS	LT1214CN	LT1223CS8	LT1253CN8
LT1206CN8	LT1214CS	LT1223MJ8	LT1253CS8
LT1206CR	LT1215ACN8	LT1224CN8	LT1254CN
LT1206CS8	LT1215AMJ8	LT1224CS8	LT1254CS
LT1206CY	LT1215CN8	LT1225CN8	LT1256CN
LT1207CS	LT1215CS8	LT1225CS8	LT1256CS
LT1208CN8	LT1215MJ8	LT1226CN8	LT1259CN
LT1208CS8	LT1216CN	LT1226CS8	LT1259CS
LT1209CN	LT1216CS	LT1227CN8	LT1260CN
LT1209CS	LT1217CN8	LT1227CS8	LT1260CS
LT1210CR	LT1217CS8	LT1227MJ8	LT1328CMS8
LT1210CS	LT1218CN8	LT1228CN8	LT1328CS8
LT1210CT7	LT1218CS8	LT1228CS8	LT1351CMS8
LT1211ACN8	LT1219CN8	LT1229CJ8	LT1351CN8
LT1211AMJ8	LT1219CS8	LT1229CN8	LT1351CS8
LT1211CN8	LT1220CN8	LT1229CS8	LT1352CN8
LT1211CS8	LT1220CS8	LT1229MJ8	LT1352CS8
LT1211MJ8	LT1220MJ8	LT1230CJ	LT1353CS
LT1212CN	LT1221CN8	LT1230CN	LT1354CN8
LT1212CS	LT1221CS8	LT1230CS	LT1354CS8

Multisim 14.0 Full Components

LT1355CN8	LT1367CS	LT1461-33	LT1491CN
LT1355CS8	LT1368CN8	LT1461-4	LT1491CS
LT1356CN	LT1368CS8	LT1461-5	LT1492CN8
LT1356CS	LT1369CS	LT1462CN8	LT1492CS8
LT1357CN8	LT1394CMS8	LT1462CS8	LT1493CS
LT1357CS8	LT1395CS5	LT1463CN	LT1494CMS8
LT1358CN8	LT1395CS6	LT1463CS	LT1494CN8
LT1358CS8	LT1395CS8	LT1464CN8	LT1494CS8
LT1359CN	LT1396CDD	LT1464CS8	LT1495CN8
LT1359CS	LT1396CMS8	LT1465CN	LT1495CS8
LT1359CS14	LT1396CS8	LT1465CS	LT1496CN
LT1360CN8	LT1397CGN	LT1466LCN8	LT1496CS
LT1360CS8	LT1397CS	LT1466LCS8	LT1497CS
LT1361CN8	LT1398CS	LT1467LCS	LT1497CS8
LT1361CS8	LT1399CGN	LT1468CDD	LT1498CN8
LT1362CN	LT1399CS	LT1468CN8	LT1498CS8
LT1362CS	LT1413ACN8	LT1468CS8	LT1499CS
LT1363CN8	LT1413CN8	LT1468IDD	LT1521CMS8
LT1363CS8	LT1413S8	LT1468IN8	LT1521CS8
LT1364CN8	LT1431CN8	LT1468IS8	LT1529CQ
LT1364CS8	LT1431CS8	LT1469CN8	LT1529CT
LT1365CN	LT1457CN8	LT1469CS8	LT1568CGN
LT1365CS	LT1457S8	LT1490CMS8	LT1568IGN
LT1366CN8	LT1461-25	LT1490CN8	LT1630CN8
LT1366CS8	LT1461-3	LT1490CS8	LT1630CS8

Multisim 14.0 Full Components

LT1631CS	LT1672IMS8	LT1720CS8	LT1762EMS8-2.5
LT1632CN8	LT1672IN8	LT1720IDD	LT1762EMS8-3
LT1632CS8	LT1672IS8	LT1720IMS8	LT1762EMS8-3.3
LT1633CS	LT1673CN8	LT1720IS8	LT1762EMS8-5
LT1635CN8	LT1673CS8	LT1721CGN	LT1763CDE
LT1635CS8	LT1673IN8	LT1721CS	LT1763CDE-1.5
LT1636CDD	LT1673IS8	LT1721IGN	LT1763CDE-1.8
LT1636CMS8	LT1674CN	LT1722CS5	LT1763CDE-2.5
LT1636CN8	LT1674CS	LT1722CS8	LT1763CDE-3
LT1636CS8	LT1674IN	LT1723CMS8	LT1763CDE-3.3
LT1637CDD	LT1674IS	LT1723CS8	LT1763CDE-5
LT1637CMS8	LT1677CN8	LT1724CS	LT1763CS8
LT1637CN8	LT1677CS8	LT1739CFE	LT1763CS8-1.5
LT1637CS8	LT1678CS8	LT1739CUE	LT1763CS8-1.8
LT1638CDD	LT1679CS	LT1739IFE	LT1763CS8-2.5
LT1638CMS8	LT1711CMS8	LT1739IUE	LT1763CS8-3
LT1638CN8	LT1712CGN	LT1761ES5-1.8	LT1763CS8-3.3
LT1638CS8	LT1713CMS8	LT1761ES5-2	LT1763CS8-5
LT1639CN	LT1714CGN	LT1761ES5-2.5	LT1763IS8
LT1639CS	LT1715CMS	LT1761ES5-3	LT1763IS8-1.5
LT1671CMS8	LT1716CS5	LT1761ES5-3.3	LT1763IS8-1.8
LT1671CS8	LT1719CS8	LT1761ES5-5	LT1764EFE
LT1672CMS8	LT1719IS8	LT1761ES5-BYP	LT1764EFE-1.5
LT1672CN8	LT1720CDD	LT1761ES5-SD	LT1764EFE-1.8
LT1672CS8	LT1720CMS8	LT1762EMS8	LT1764EFE-2.5

Multisim 14.0 Full Components

LT1764EFE-3.3	LT1794CSW	LT1814CS	LT1819IMS8
LT1764EQ	LT1795CFE	LT1815CS5	LT1819IS8
LT1764EQ-1.5	LT1795CSW	LT1815CS6	LT1880CS5
LT1764EQ-1.8	LT1797CS5	LT1815CS8	LT1881CN8
LT1764EQ-2.5	LT1800CS5	LT1815IS5	LT1881CS8
LT1764EQ-3.3	LT1800CS8	LT1815IS6	LT1882CS
LT1782CS6	LT1801CDD	LT1815IS8	LT1884CN8
LT1783CS6	LT1801CMS8	LT1816ACMS	LT1884CS8
LT1784CS6	LT1801CS8	LT1816AIMS	LT1885CS
LT1784IS6	LT1802CS	LT1816CDD	LT1886CS8
LT1787CMS8	LT1806CS6	LT1816CMS8	LT1920CN8
LT1789CS8-1	LT1806CS8	LT1816CS8	LT1920CS8
LT1789CS8-10	LT1807CMS8	LT1816IDD	LT1962EMS8
LT1790ACS6-1.25	LT1807CS8	LT1816IMS8	LT1962EMS8-1.5
LT1790ACS6-2.048	LT1809CS6	LT1816IS8	LT1962EMS8-1.8
LT1790ACS6-2.5	LT1809CS8	LT1817CGN	LT1962EMS8-2.5
LT1790ACS6-3	LT1810CMS8	LT1817CS	LT1962EMS8-3
LT1790ACS6-3.3	LT1810CS8	LT1817IGN	LT1962EMS8-3.3
LT1790ACS6-4.096	LT1812CS5	LT1817IS	LT1962EMS8-5
LT1790ACS6-5	LT1812CS6	LT1818CS5	LT1963EFE
LT1792CN8	LT1812CS8	LT1818CS8	LT1963EFE-1.5
LT1792CS8	LT1813CDD	LT1818IS5	LT1963EFE-1.8
LT1793CN8	LT1813CS8	LT1818IS8	LT1963EFE-2.5
LT1793CS8	LT1813DMS8	LT1819CMS8	LT1963EFE-3.3
LT1794CFE	LT1814CGN	LT1819CS8	LT1970CFE

Multisim 14.0 Full Components

LT1990CS8	LT318AN8	LT6005HDHC	LT6203CS8
LT1991CDD	LT6000CDCB	LT6005HGN	LT6204CGN
LT1991CMS	LT6000IDCB	LT6005IDHC	LT6204CS
LT1993CUD-10	LT6001CDD	LT6005IGN	LT6205CS5
LT1993CUD-2	LT6001CMS8	LT6010CDD	LT6206CMS8
LT1993CUD-4	LT6001IDD	LT6010CS8	LT6207CGN
LT1994CDD	LT6001IMS8	LT6011CDD	LT6220CS5
LT1994CMS8	LT6002CDHC	LT6011CMS8	LT6220CS8
LT1995CDD	LT6002CGN	LT6011CS8	LT6221CDD
LT1995CMS	LT6002IDHC	LT6012CGN	LT6221CS8
LT1995IDD	LT6002IGN	LT6012CS	LT6222CGN
LT1995IMS	LT6003CDC	LT6100CDD	LT6230CS6
LT1996CDD	LT6003CS5	LT6100CMS8	LT6231CDD
LT1996CMS	LT6003HDC	LT6200CS6	LT6231CS8
LT2078ACS8	LT6003HS5	LT6200CS6-10	LT6232CGN
LT2078AIS8	LT6003IDC	LT6200CS6-5	LT6233CS6
LT2078CS8	LT6003IS5	LT6200CS8	LT6234CDD
LT2079ACS	LT6004CDD	LT6200CS8-10	LT6234CS8
LT2079CS	LT6004CMS8	LT6200CS8-5	LT6235CGN
LT2178ACS8	LT6004HDD	LT6201CDD	LT6235IGN
LT2178CS8	LT6004HMS8	LT6201CS8	LT6402CUD-12
LT2179ACS	LT6004IDD	LT6202CS5	LT6402CUD-20
LT2179CS	LT6004IMS8	LT6202CS8	LT6402CUD-6
LT318A	LT6005CDHC	LT6203CDD	LT6402IUD-12
LT318AJ8	LT6005CGN	LT6203CMS8	LT6402IUD-20

Multisim 14.0 Full Components

LT6402IUD-6	LT6700CDCB-3	LTC1051ACS	LTC1250CS8
LT6411CUD	LT6700CS6-1	LTC1051AMJ8	LTC1440CDD
LT6411IUD	LT6700CS6-2	LTC1051CJ8	LTC1440CMS8
LT6552CDD	LT6700CS6-3	LTC1051CN8	LTC1440CN8
LT6552CS8	LTC1043CN	LTC1051CS	LTC1440CS8
LT6552IDD	LTC1043CSW	LTC1051MJ8	LTC1441CN8
LT6552IS8	LTC1047CN8	LTC1052CD	LTC1441CS8
LT6553CGN	LTC1047CS	LTC1052CP	LTC1442CN8
LT6553IGN	LTC1049CJ8	LTC1052CS	LTC1442CS8
LT6557CDHC	LTC1049CN8	LTC1052MD	LTC1443CDHD
LT6557CGN	LTC1049CS8	LTC1052MP	LTC1443CN
LT6557IDHC	LTC1050ACH	LTC1053CN	LTC1443CS
LT6557IGN	LTC1050ACJ8	LTC1053CS	LTC1444CDHD
LT6558CDHC	LTC1050ACN	LTC1053CSW	LTC1444CN
LT6558CGN	LTC1050ACN8	LTC1100CN8	LTC1444CS
LT6558IDHC	LTC1050AMH	LTC1100CSW	LTC1444IDHD
LT6558IGN	LTC1050AMJ8	LTC1150CJ8	LTC1444IN
LT6559CUD	LTC1050CH	LTC1150CN8	LTC1444IS
LT6600-10	LTC1050CJ8	LTC1150CS8	LTC1445CDHD
LT6600-2.5	LTC1050CN	LTC1150MJ8	LTC1445CN
LT6600-20	LTC1050CN8	LTC1151CN8	LTC1445CS
LT6600-5	LTC1050MH	LTC1151CSW	LTC152
LT6650CS5	LTC1050MJ8	LTC1152CN8	LTC1540CDD
LT6700CDCB-1	LTC1051ACJ8	LTC1152CS8	LTC1540CMS8
LT6700CDCB-2	LTC1051ACN8	LTC1250CN8	LTC1540CS8

Multisim 14.0 Full Components

LTC1541CDD	LTC2053CMS8	LTC6242CGN	M37702S1BFP
LTC1541CMS8	LTC2053HDD	LTC6242HGN	M6060P-E3/45
LTC1541CS8	LTC2053HMS8	LTC6242IDHC	M68AF031AL_SO28
LTC1542CDD	LTC2053IMS8-SYNC	LTC6242IGN	M68AF127BL_SO32
LTC1542CMS8	LTC2054CS5	LTC6244CDD	M68AF511AL_SO32
LTC1542CS8	LTC2055CDD	LTC6244CMS8	M68AW031AL_SO28
LTC1563-2CGN	LTC2055CMS8	LTC6244HMS8	M68AW064FL_FBG A48
LTC1563-3CGN	LTC6078CDD	LTC6244IDD	M68AW128ML_SO44
LTC1798CS8	LTC6078CMS8	LTC6244IMS8	M68AW256ML_SO44
LTC1798CS8-2.5	LTC6079CDHC	LTC6800HDD	M68AW511AL_SO32
LTC1798CS8-3	LTC6079CGN	LTC6800HMS8	M68AW512DL_FBG A48
LTC1798CS8-4.1	LTC6101ACMS8	LTC6910-1CTS8	M68AW512ML_SO44
LTC1798CS8-5	LTC6101BCS5	LTC6910-2CTS8	MAC08MT1G
LTC1841CS8	LTC6240CS5	LTC6910-3CTS8	MAC12HCDG
LTC1842CS8	LTC6240CS8	LTC6911CMS-1	MAC15-10
LTC1966CMS8	LTC6240HS5	LTC6911CMS-2	MAC15-4
LTC1967CMS8	LTC6240HS8	LTC7652CH	MAC15-6
LTC1968CMS8	LTC6240IS5	LTR-516AD	MAC15-8
LTC2050CS5	LTC6240IS8	LVL_BARGRAPH	MAC15A-10
LTC2050CS6	LTC6241CDD	LVM_CURRENT	MAC15A-4
LTC2050CS8	LTC6241CS8	LVM_VOLTAGE	
LTC2051CMS10	LTC6241HS8	LVT22V10-7A	
LTC2052CGN	LTC6241IDD	LVT22V10-7N	
LTC2052CS	LTC6241IS8	LVT22V10B7A	
LTC2053CDD	LTC6242CDHC	M37702S1AFP	

Multisim 14.0 Full Components

MAC15A-8	MAC224-4	MAT04AY	MAX1449_FP32
MAC210-10	MAC224-6	MAT04EY	MAX14802ECM+
MAC210-4	MAC224-8	MAT04FP	MAX14803AEWZ+
MAC210-6	MAC224A-10	MAT04FS	MAX14803CCM+
MAC210-8	MAC224A-4	MAT04FY	MAX15006AASA+
MAC210A-10	MAC224A-6	MAX1180_FP48	MAX15006AATT+
MAC210A-4	MAC224A-8	MAX1181_FP48	MAX15007AASA+
MAC210A-6	MAC228-10	MAX1182_FP48	MAX15007AATT+
MAC210A-8	MAC228-4	MAX1183_FP48	MAX15024AATB+
MAC212-10	MAC228-6	MAX1184_FP48	MAX15024BATB+
MAC212-4	MAC228-8	MAX1185_FP48	MAX15024CATB+
MAC212-6	MAC228A-10	MAX1195_FP48	MAX15024DATB+T
MAC212-8	MAC228A-4	MAX1197_FP48	MAX15025CATB+T
MAC212A-10	MAC228A-6	MAX1198_FP48	MAX16010TAA+
MAC212A-4	MAC228A-8	MAX1284_SO8	MAX16010TAB+
MAC212A-6	MAC23A-10	MAX1285_SO8	MAX16010TAC+
MAC212A-8	MAG_CMP4	MAX1290_SO28	MAX1666VEEP
MAC223-10	MAG_OL	MAX1291_SO28	MAX1966_SO8
MAC223-4	MAG_OL_RELAY	MAX1292_SO24	MAX1967_SO10
MAC223-6	MAGNETIC_CORE_VIRTUAL	MAX1293_SO24	MAX200CPP
MAC223-8	MAT02EH	MAX1420_FP48	MAX200ECWP
MAC223A-4	MAT02FH	MAX1421_FP48	MAX200EEWP
MAC223A-6	MAT03EH	MAX1422_FP48	MAX200EPP
MAC223A-8	MAT03FH	MAX1444_FP32	MAX201CPD
MAC224-10		MAX1446_FP32	MAX201CWE

Multisim 14.0 Full Components

MAX201EPD	MAX205CPG	MAX209ENG	MAX221EEUE
MAX201EWE	MAX205E	MAX211	MAX232E
MAX202CPE	MAX205ECAG	MAX211CAI	MAX232ECPE
MAX202CSE	MAX205ECWG	MAX211E	MAX232EEPE
MAX202CWE	MAX205EEAG	MAX211EAI	MAX241E
MAX202ECPE	MAX205EEWG	MAX211ECAI	MAX241ECAI
MAX202ECUE	MAX206	MAX211ECWI	MAX241ECWI
MAX202EEPE	MAX206CAG	MAX211EEAI	MAX241EEAI
MAX202EEUE	MAX206E	MAX211EEWI	MAX241EEWI
MAX202ESE	MAX206EAG	MAX213	MAX253CPA+
MAX202EWE	MAX207	MAX213CAI	MAX253CSA+
MAX202SE	MAX207CAG	MAX213E	MAX253CUA+
MAX203CPP	MAX207E	MAX213EAI	MAX253EPA+
MAX203CWP	MAX207EAG	MAX213ECAI	MAX253ESA+
MAX203E	MAX207ECAG	MAX213ECWI	MAX253EUA+
MAX203ECPP	MAX207EEAG	MAX213EEAI	MAX253MJA
MAX203ECWP	MAX208	MAX213EEWI	MAX253MSA/PR
MAX203EPP	MAX208CAG	MAX218	MAX263_DIP28
MAX203EWP	MAX208E	MAX218CAP	MAX264_DIP28
MAX203EPP	MAX208EAG	MAX218CPP	MAX267_DIP24
MAX203EWP	MAX208ECAG	MAX218EAP	MAX268_DIP24
MAX204CPE	MAX208ECWG	MAX218EPP	MAX2740ECM
MAX204CWE	MAX208EEAG	MAX221ECAE	MAX274ACNG
MAX204EPE	MAX208EEWG	MAX221ECUE	MAX274ACWI
MAX204EWE	MAX209	MAX221EEAE	MAX274BCNG

Multisim 14.0 Full Components

MAX274BCWI	MAX319EPA+	MAX3223EEPP	MAX4016EUA+
MAX280_SO16	MAX319ESA+	MAX3223EEUP	MAX4018EEE+
MAX281A_SO16	MAX319MJA	MAX3232	MAX4018ESD+
MAX291_SO16	MAX3212	MAX3232E	MAX4020EEE+
MAX292_SO16	MAX3212CAI	MAX3237	MAX4020ESD+
MAX295_SO16	MAX3212EAI	MAX3237E	MAX4023EEE+
MAX296_SO16	MAX3218	MAX3238E	MAX4023ESE+
MAX317CJA	MAX3218CAP	MAX3241	MAX4024ESD+
MAX317CPA+	MAX3218CPP	MAX3241E	MAX4024EUD+
MAX317CSA+	MAX3218EAP	MAX3243	MAX4027ESD+
MAX317EJA	MAX3218EPP	MAX3243E	MAX4027EUD+
MAX317EPA+	MAX3221	MAX3243ECAI	MAX4028EUE+
MAX317ESA+	MAX3221CAE	MAX3243ECAP	MAX4028EWE+
MAX317MJA	MAX3221E	MAX3243ECPP	MAX4029EUP+
MAX318CJA	MAX3221EAE	MAX3243EEAI	MAX4029EWP+
MAX318CPA+	MAX3221ECAE	MAX3248E	MAX402CPA
MAX318CSA+	MAX3221EEAE	MAX3380E	MAX402CSA
MAX318EJA	MAX3222	MAX3381E	MAX402EPA
MAX318EPA	MAX3222E	MAX4004EUT+	MAX402ESA
MAX318ESA+	MAX3223	MAX4006EUT+	MAX4032EUT+
MAX318MJA	MAX3223E	MAX4007EUT+	MAX4032EXT+
MAX319CJA	MAX3223ECAP	MAX4008EUT+	MAX4036AAXK+
MAX319CPA+	MAX3223ECPP	MAX4012ESA+	MAX4036EXK+
MAX319CSA+	MAX3223ECUP	MAX4012EUK+	MAX4037EUT+
MAX319EJA	MAX3223EEAP	MAX4016ESA+	MAX4038AAUA+

Multisim 14.0 Full Components

MAX4038EBL+T	MAX4072ATA+	MAX4090EUT+	MAX4108ESA
MAX4038ETA+	MAX4072AUA+	MAX4090EXT+	MAX4108ESA+
MAX4038EUA+	MAX4073TAUT+	MAX409ACPA+	MAX4109ESA+
MAX4039EBL+T	MAX4073TAXK+	MAX409ACSA+	MAX410BCPA
MAX4039ETB+T	MAX407CPA+	MAX409AEPA	MAX410BCSA
MAX4039EUB+	MAX407CSA+	MAX409AESA+	MAX410BCSA+
MAX403CPA	MAX407EPA+	MAX409AMJA	MAX410BEPA
MAX403CSA	MAX407ESA+	MAX409BCPA+	MAX410BESA
MAX403EPA	MAX407MJA	MAX409BCSA+	MAX410CPA
MAX403ESA	MAX4080FASA+	MAX409BEPA+	MAX410CPA+
MAX4069AUB+	MAX4080FAUA+	MAX409BESA+	MAX410CSA
MAX406ACPA+	MAX4080SASA+	MAX4100ESA	MAX410CSA+
MAX406ACSA+	MAX4080SAUA+	MAX4100ESA+	MAX410EPA
MAX406AEPA+	MAX4080TASA+	MAX4100EUA+	MAX410EPA+
MAX406AESA+	MAX4080TAUA+	MAX4101ESA	MAX410ESA+
MAX406AMJA	MAX4081FASA+	MAX4101ESA+	MAX410ETA-T
MAX406BCPA+	MAX4081FAUA+	MAX4104ESA	MAX4112ESA+
MAX406BCSA+	MAX4081SASA+	MAX4104ESA+	MAX4112EUA
MAX406BEPA+	MAX4081SAUA+	MAX4104EUK+	MAX4113ESA+
MAX406BESA+	MAX4081TASA+	MAX4105ESA+	MAX4117ESA+
MAX406BMJA	MAX4081TAUA+	MAX4105EUK+T	MAX4118ESA+
MAX4070ATA+	MAX4090AALT+T	MAX4106ESA	MAX4119EEE
MAX4070AUA+	MAX4090AAUT+	MAX4106ESA+	MAX4119ESD+
MAX4071ATA+	MAX4090AAXT+	MAX4107ESA	MAX4120ESD+
MAX4071AUA+	MAX4090ELT+T	MAX4107ESA+	MAX4122EUK+

Multisim 14.0 Full Components

MAX4124EUK+	MAX4131ESA+	MAX414EPD+	MAX4178EPA+
MAX4126ESA+	MAX4131EUA+	MAX414ESD	MAX4178ESA+
MAX4126EUA+	MAX4132ESA+	MAX414ESD+	MAX4178EUA+
MAX4128ESA+	MAX4132EUA+	MAX414MJD	MAX4178EUK+T
MAX4128EUA+	MAX4133ESD	MAX4162ESA+	MAX4178MJA
MAX4129ESD+	MAX4134ESD+	MAX4162EUK+	MAX417CPA+
MAX412BCPA	MAX4144EEE+	MAX4163EBL+	MAX417CSA+
MAX412BCPA+	MAX4144ESD+	MAX4163ESA+	MAX417EPA+
MAX412BCSA	MAX4145EEE+	MAX4163EUA+	MAX417ESA+
MAX412BCSA+	MAX4145ESD+	MAX4164ESD+	MAX417MJA
MAX412BEPA	MAX4146EEE+	MAX4165EUK+	MAX4180ESA+
MAX412BEPA+	MAX4146ESD+	MAX4166ELA+	MAX4180EUT+T
MAX412BESA	MAX4147ESD	MAX4166EPA+	MAX4181ESA+
MAX412BESA+	MAX4147ESD+	MAX4166ESA+	MAX4181EUT+T
MAX412CPA	MAX414BCPD	MAX4166EUA+	MAX4182ESA+
MAX412CPA+	MAX414BCSD	MAX4167EPA+	MAX4183ESD+
MAX412CSA	MAX414BCSD+	MAX4167ESA+	MAX4183EUB+
MAX412CSA+	MAX414BEPD	MAX4168EPD+	MAX4184ESA+
MAX412EPA	MAX414BESD	MAX4168ESD+	MAX4185ESD
MAX412EPA+	MAX414BESD+	MAX4168EUB+	MAX4185EUB+
MAX412ESA	MAX414CPD	MAX4169EPD	MAX4186ESD+
MAX412ESA+	MAX414CPD+	MAX4169ESD+	MAX4187EEE+
MAX412MJA	MAX414CSD	MAX4172EUA+	MAX4187ESD+
MAX4130EUK+	MAX414CSD+	MAX4173TESA+	MAX4188EEE+
MAX4131EBT+	MAX414EPD	MAX4173TEUT+	MAX4188ESD+

Multisim 14.0 Full Components

MAX4189EEE+	MAX4201EUK+T	MAX4220ESD+	MAX4236AESA+
MAX4189ESD+	MAX4202ESA+	MAX4222EEE+	MAX4236AEUA
MAX418CPD+	MAX4202EUK+T	MAX4222ESD+	MAX4236BESA+
MAX418CSD+	MAX4203ESA+	MAX4223ESA+	MAX4236BEUA+
MAX418EPD+	MAX4203EUA+	MAX4223EUT+	MAX4236EUT+
MAX418ESD+	MAX4204ESA+	MAX4224ESA+	MAX4237AESA+
MAX418MJD	MAX4204EUA+	MAX4224EUT+	MAX4237AEUA+
MAX4190ESA+	MAX4205ESA	MAX4225ESA+	MAX4237BESA+
MAX4190EUA	MAX4205EUA+	MAX4226ESD	MAX4237BEUA+
MAX4194ESA+	MAX4206ETE	MAX4226EUB+	MAX4237EUT+
MAX4195ESA+	MAX4212EUK+	MAX4227ESA+	MAX4238ASA+
MAX4196ESA+	MAX4213ESA+	MAX4228ESD+	MAX4238ATT+
MAX4197ESA+	MAX4213EUA+	MAX4228EUB+	MAX4238AUT+
MAX4198ESA+	MAX4214EUK+	MAX4230AUK+	MAX4239ASA+
MAX4198EUA+	MAX4215ESA+	MAX4230AXK+	MAX4239ATT+
MAX4199ESA+	MAX4215EUA+	MAX4231ART+T	MAX4239AUT+
MAX4199EUA+	MAX4216ESA+	MAX4231AUT+	MAX4240EUK+
MAX419CPD+	MAX4216EUA+	MAX4231AXT+	MAX4241ESA+
MAX419CSD+	MAX4217ESA+	MAX4231AYT+	MAX4241EUA+
MAX419EPD+	MAX4217EUA+	MAX4232AKA+	MAX4242ESA+
MAX419ESD+	MAX4218EEE+	MAX4232AUA+	MAX4242EUA+
MAX419MJD	MAX4218ESD+	MAX4233ABC+T	MAX4243ESD
MAX4200ESA+	MAX4219EEE+	MAX4233AUB+	MAX4243EUB+
MAX4200EUK+	MAX4219ESD+	MAX4234ASD+	MAX4244ESD+
MAX4201ESA+	MAX4220EEE+	MAX4234AUD+	MAX4245AUT+

Multisim 14.0 Full Components

MAX4245AXT+	MAX4267EUA	MAX4286ESA+	MAX4331EUA+
MAX4247AUB+	MAX4268EEE+	MAX4286EUT-T	MAX4332ESA+
MAX4249ESD+	MAX4268ESD+	MAX4288ESD	MAX4333ESD+
MAX4249EUB+	MAX4269EEE	MAX4288EUB	MAX4333EUB+
MAX4250AAUK+	MAX4269ESD	MAX4289ESA+	MAX4334ESD+
MAX4250EUK+	MAX4270EEE	MAX4289EUT+	MAX4335EXT+
MAX4251ESA+	MAX4270ESD	MAX4291EUK+	MAX4336EUT-T
MAX4251EUA+	MAX4278EPA+	MAX4291EXK+	MAX4336EXT+
MAX4252EBL+	MAX4278ESA+	MAX4292EBL+	MAX4337EKA+
MAX4252ESA+	MAX4278EUA+	MAX4292ESA+	MAX4337EUA+
MAX4252EUA+	MAX4278EUK+	MAX4292EUA+	MAX4338EUB+
MAX4253EBC+	MAX4278MJA	MAX4294ESD+	MAX435CPD
MAX4253ESD+	MAX427CPA+	MAX4294EUD+	MAX435CSD
MAX4253EUB+	MAX427CSA+	MAX4304ESA+	MAX435CSD+
MAX4254ESD+	MAX427EPA+	MAX4304EUK+	MAX435EPD
MAX4255EUK+	MAX427ESA+	MAX4305ESA+	MAX435ESD
MAX4256ESA+	MAX427MJA	MAX4305EUK+	MAX435ESD+
MAX4256EUA+	MAX4281ESA+	MAX4323EBT+T	MAX435MJD
MAX4257ESA+	MAX4281EUK+	MAX4323ESA+	MAX4361
MAX4257EUA+	MAX4282ESA+	MAX4323EUA	MAX4361_SO8
MAX4265ESA+	MAX4282EUA+	MAX4323EUT+	MAX4361ESA
MAX4265EUA+	MAX4284EEE	MAX4327ESD	MAX4361EUA
MAX4266ESA+	MAX4284ESD	MAX4327EUB+	MAX4362ESD+
MAX4266EUA+	MAX4285ESA+	MAX4330EUK+	MAX4362EUB+
MAX4267ESA+	MAX4285EUT+	MAX4331ESA+	MAX4363EUP+

Multisim 14.0 Full Components

MAX436CPD	MAX4374HEUB+	MAX4385EEUK+	MAX4412EUK+
MAX436CSD	MAX4374TESD+	MAX4386EESD+	MAX4412EXK+
MAX436CSD+	MAX4374TEUB+	MAX4386EEUD+	MAX4413EKA+
MAX436EPD	MAX4375FESD+	MAX4388ESD+	MAX4414ESA+
MAX436ESD	MAX4375FEUB+	MAX4388EUB	MAX4414EUA+
MAX436ESD+	MAX4375HESD+	MAX4389EUT+	MAX4415ESA+
MAX436MJD	MAX4375HEUB+	MAX4389EXT+	MAX4415EUA+
MAX4372FEBT+T	MAX4375TESD+	MAX4390EUK+	MAX4416ESA+
MAX4372FESA+	MAX4375TEUB+	MAX4390EXT+	MAX4416EUA+
MAX4372FEUK+	MAX437CPA	MAX4392ESA+	MAX4417ESA+
MAX4372HEBT+T	MAX437CSA+	MAX4392EUA+	MAX4417EUA+
MAX4372HESA+	MAX437EPA	MAX4393EUB+	MAX4418EUD+
MAX4372HEUK+	MAX437ESA+	MAX4394ESD+	MAX4419EUD+
MAX4372TEBT+T	MAX437MJA	MAX4394EUD+	MAX44241AUA+
MAX4372TESA+	MAX4380EUT+	MAX4395ESD+	MAX44241AUK+T
MAX4372TEUK+	MAX4380EXT+	MAX4395EUD+	MAX44243ASD+
MAX4373FESA+	MAX4381EUB+	MAX4396EUP+	MAX44243AUD+
MAX4373FEUA+	MAX4382EEE+	MAX4400AUK+	MAX44251AKA+
MAX4373HESA+	MAX4382ESD+	MAX4400AXK+	MAX44251AUA+
MAX4373HEUA+	MAX4382EUD+	MAX4401AXT+	MAX44252ASD+
MAX4373TESA+	MAX4383EEE+	MAX4402AKA+	MAX44264EWT+
MAX4373TEUA+	MAX4383ESD+	MAX4402ASA+	MAX44265EWT+
MAX4374FESD+	MAX4383ESE+	MAX4402AUA+	MAX44269EWL+
MAX4374FEUB+	MAX4383EUD+	MAX4403ASD+	MAX44280AXT+
MAX4374HESD+	MAX4384EUP+	MAX4403AUD+	MAX44280AYT+

Multisim 14.0 Full Components

MAX44281OANS+	MAX4450EXK+	MAX4462TETT+T	MAX4482AKA+
MAX44281UANS+	MAX4451EKA+	MAX4462TEUT	MAX4482ASA+
MAX44281VANS+	MAX4451ESA+	MAX4462UESA	MAX4482AUA+
MAX44285FAUA+	MAX4452EUK+	MAX4462UETT+	MAX4483ASD+
MAX44285FAWA+T	MAX4452EXK+	MAX4464EUK+	MAX4483AUD+
MAX44285HAUA+	MAX4453EKA+	MAX4464EXK+	MAX4484AUK+
MAX44285HAWA+T	MAX4453ESA+	MAX4473ESA	MAX4484AXK+
MAX44285LAUA+	MAX4454ESD+	MAX4473EUA+	MAX4486AKA+
MAX44285LAWA+T	MAX4454EUD+	MAX4474EKA+	MAX4486ASA+
MAX44285TAUA+	MAX4460ESA+	MAX4474ESA+	MAX4486AUA+
MAX44285TAWA+T	MAX4460ETT+	MAX4474EUA+	MAX4487ASD+
MAX4430ESA+	MAX4460EUT+T	MAX4475ASA+	MAX4487AUD+
MAX4430EUK+	MAX4461HESA+	MAX4475ATT+	MAX4488ASA+
MAX4432ESA	MAX4461HETT+T	MAX4475AUA+	MAX4488ATT+
MAX4432EUA+	MAX4461HEUT+	MAX4475AUT+	MAX4488AUA+
MAX4434ESA	MAX4461TESA+	MAX4476ATT+T	MAX4488AUT+
MAX4434EUK+	MAX4461TETT+	MAX4476AUT+	MAX4489ASA+
MAX4435ESA	MAX4461TEUT	MAX4477ASA+	MAX4489AUA+
MAX4435EUK	MAX4461UESA+	MAX4477AUA+	MAX4490AUK+T
MAX4436ESA	MAX4461UETT+T	MAX4478ASD+	MAX4490AXK+
MAX4436EUA+	MAX4461UEUT-T	MAX4478AUD+	MAX4491AKA+
MAX4437ESA	MAX4462HESA+	MAX4480AUK+	MAX4491AUA+
MAX4437EUA+	MAX4462HETT+	MAX4480AXK+	MAX4492ASD+
MAX4444ESE+	MAX4462HEUT+	MAX4481AUT+	MAX4492AUD+
MAX4450EUK+	MAX4462TESA	MAX4481AXT+	MAX4493AUK

Multisim 14.0 Full Components

MAX4493AXK+	MAX4543EPA	MAX4667CPE	MAX4718EUB
MAX4494AKA+	MAX4543ESA+	MAX4667CSE	MAX4719EBC-T
MAX4494ASA+	MAX4543EUA+	MAX4667EPE	MAX4719EUB+
MAX4494AUA+	MAX4601CAE+	MAX4667ESE+	MAX473CPA
MAX4495ASD+	MAX4601CPE+	MAX4668CPE+	MAX473CPA+
MAX4495AUD+	MAX4601CWE+	MAX4668CSE+	MAX473CSA
MAX4541CPA+	MAX4601EAE+	MAX4668EPE+	MAX473CSA+
MAX4541CSA+	MAX4601EPE+	MAX4668ESE+	MAX473CUA
MAX4541CUA+	MAX4601EWE	MAX4669CPE	MAX473CUA+
MAX4541EKA+	MAX4602CAE+	MAX4669CSE+	MAX473EPA+
MAX4541EPA	MAX4602CPE+	MAX4669EPE	MAX473ESA+
MAX4541ESA+	MAX4602CWE+	MAX4669ESE+	MAX473MJA
MAX4541ETA+T	MAX4602EAE+	MAX4670ETJ+	MAX474CPA
MAX4541EUA	MAX4602EPE	MAX4684EBC+	MAX474CPA+
MAX4541EUA+	MAX4602EWE+	MAX4684ETB+	MAX474CSA
MAX4542CSA+	MAX4603CAE+	MAX4684EUB+	MAX474CSA+
MAX4542CUA	MAX4603CPE+	MAX4685EBC+T	MAX474CUA
MAX4542EKA+	MAX4603CWE+	MAX4685ETB+T	MAX474CUA+
MAX4542EPA	MAX4603EAE+	MAX4685EUB+	MAX474EPA+
MAX4542ESA+	MAX4603EPE+	MAX4714ELT+	MAX474ESA+
MAX4542EUA+	MAX4603EWE+	MAX4714EXT+	MAX474MJA
MAX4543CPA	MAX4659ESA+	MAX4717EBC+	MAX4754AEBE+T
MAX4543CSA	MAX4659EUA+	MAX4717ETB+	MAX4754AETE+
MAX4543CUA	MAX4660ESA+	MAX4717EUB+	MAX4754EBE+T
MAX4543EKA+	MAX4660EUA+	MAX4718EBC-T	MAX4754ETE+

Multisim 14.0 Full Components

MAX475CPD	MAX4818ETE+	MAX494ESD+	MAX6324AUT23-T
MAX475CSD	MAX4819ETE	MAX494MJD	MAX6324AUT26-T
MAX475EPD	MAX4885EETG+	MAX4951CTP+	MAX6324AUT29+T
MAX475ESD	MAX4885ETJ+	MAX495CPA	MAX6324AUT31+T
MAX475MJD	MAX4887ETE+	MAX495CPA+	MAX6324AUT44-T
MAX477EPA+	MAX4889AETO+	MAX495CSA	MAX6324AUT46+T
MAX477ESA+	MAX4890ETJ+	MAX495CSA+	MAX6324BUT23+T
MAX477EUA+	MAX4891ETJ+	MAX495CUA	MAX6324BUT26-T
MAX477EUK+T	MAX4892ETX+	MAX495CUA+	MAX6324BUT29+T
MAX477MJA	MAX4906FELB+	MAX495EPA+	MAX6324BUT31-T
MAX478ACPA+	MAX4906FETB+T	MAX495ESA+	MAX6324BUT44-T
MAX478CPA+	MAX4907FELA+	MAX495MJA	MAX6324BUT46+T
MAX478CSA+	MAX4907FETA+T	MAX496CPE+	MAX6324CUT23+T
MAX478EPA+	MAX492CPA	MAX496CSE+	MAX6324CUT26+T
MAX478ESA+	MAX492CPA+	MAX497CPE+	MAX6324CUT29-T
MAX479ACPD	MAX492CSA	MAX497CSE+	MAX6324CUT31-T
MAX479CPD+	MAX492CSA+	MAX5048AATT+	MAX6324CUT44-T
MAX479CSD+	MAX492EPA+	MAX5048AAUT+T	MAX6324CUT46+T
MAX479EPD+	MAX492ESA+	MAX5054AATA+	MAX6324DUT23+T
MAX479ESD+	MAX492MJA	MAX5064AATC+	MAX6324DUT26+T
MAX4800CCM+	MAX494CPD	MAX5078AATT+	MAX6324DUT29-T
MAX4800CQI+	MAX494CPD+	MAX5078BATT+	MAX6324DUT31-T
MAX4800CTM+	MAX494CSD	MAX5631_QFN68	MAX6324DUT44-T
MAX4800CXZ+	MAX494CSD+	MAX5632_QFN68	MAX6324DUT46-T
MAX4801CQI+	MAX494EPD+	MAX5633_QFN68	MAX6324EUT23+T

Multisim 14.0 Full Components

MAX6324EUT26+T	MAX6817EUT/GH9-T	MAX7407_DIP8	MAX809EUR+
MAX6324EUT29+		MAX7408_SO8	MAX809LEUR+
MAX6324EUT31-T	MAX6817EUT+	MAX7409_SO8	MAX809LEXR+
MAX6324EUT44-T	MAX6817EUT+T	MAX7410_SO8	MAX809MEUR+
MAX6324EUT46+T	MAX6817EUT-T	MAX7411_SO8	MAX809MEXR+
MAX6324FUT23+T	MAX6817EUT-TG1K	MAX7412_SO8	MAX809REUR+
MAX6324FUT26+T	MAX706RCPA	MAX7413_SO8	MAX809REXR+
MAX6324FUT29-T	MAX706RCSA+	MAX7414_SO8	MAX809SEUR+
MAX6324FUT31-T	MAX706RCUA+	MAX7415_SO8	MAX809SEXR+
MAX6324FUT44-T	MAX706REPA	MAX7418_SO8	MAX809TEUR+
MAX6324FUT46+T	MAX706RESA+	MAX7419_SO8	MAX809TEXR+
MAX6324GUT23-T	MAX706REUA+	MAX7420_SO8	MAX809ZEXR+
MAX6324GUT26+T	MAX706RMJA	MAX7421_SO8	MAX810LEUR+
MAX6324GUT29+T	MAX706TCPA+	MAX7422_SO8	MAX810LEXR+
MAX6324GUT31-T	MAX706TCSA+	MAX7423_SO8	MAX810MEUR+
MAX6324GUT44-T	MAX706TCUA+	MAX7424_SO8	MAX810MEXR+
MAX6324GUT46+T	MAX706TEPA	MAX7425_SO8	MAX810REUR+
MAX6324HUT23+T	MAX706TESA+	MAX7426_SO8	MAX810REXR+T
MAX6324HUT26-T	MAX706TEUA+	MAX7427_SO8	MAX810SEUR+
MAX6324HUT29+T	MAX706TMJA	MAX803LEXR+	MAX810SEXR+
MAX6324HUT31+T	MAX7400_DIP8	MAX803MEXR+	MAX810TEUR+
MAX6324HUT44+T	MAX7401_DIP8	MAX803REXR+	MAX810TEXR+
MAX6324HUT46+T	MAX7403_DIP8	MAX803SEXR+	MAX810ZEXR+T
MAX6460UT+	MAX7404_DIP8	MAX803TEXR+	MAX9000ESA+
MAX6780LTA+	MAX7405_DIP8	MAX803ZEXR+	MAX9000EUA+

Multisim 14.0 Full Components

MAX9002ESA+	MAX9075EUK+	MAX9092AUA+	MAX913EUA+
MAX9002EUA+	MAX9075EXK+	MAX9094ASD+	MAX913MJA
MAX9003ESA+	MAX9077EKA+	MAX9094AUD+	MAX913MSA/PR
MAX9003EUA+	MAX9077ESA+	MAX9117ESA+	MAX9140AAUK+
MAX9005ESA+	MAX9077EUA+	MAX9117EXK+	MAX9140AAXK+
MAX9005EUA+	MAX9077MSA/PR2	MAX9119EXK+	MAX9140EUK+
MAX9010EXT+	MAX907CPA	MAX9120ESA	MAX9140EXK+
MAX9011EUT+	MAX907CPA+	MAX9120EXK+	MAX9141EKA+
MAX9012ESA+	MAX907CSA	MAX912CPE	MAX9141ESA+
MAX9012EUA+	MAX907CSA+	MAX912CPE+	MAX9142EKA+
MAX9013ESA+	MAX907EPA	MAX912CSE	MAX9142ESA+
MAX9013EUA+	MAX907EPA+	MAX912CSE+	MAX9144ESD+
MAX9015AEKA+	MAX907ESA	MAX912EPE	MAX9144EUD+
MAX9026EBT+	MAX907ESA+	MAX912EPE+	MAX9201ESE+
MAX9030AUT+	MAX907MJA	MAX912ESE	MAX9201EUE+
MAX9030AXT+	MAX908CPD	MAX912ESE+	MAX9202ESD+
MAX9031AUK+	MAX908CPD+	MAX912MJE	MAX9202EUD+
MAX9031AXK+	MAX908CSD	MAX913CPA	MAX9203EKA+
MAX9032AKA+	MAX908CSD+	MAX913CPA+	MAX9203ESA+
MAX9032ASA+	MAX908EPD	MAX913CSA	MAX921CPA
MAX9032AUA+	MAX908EPD+	MAX913CSA+	MAX921CPA+
MAX9034ASD+	MAX908ESD	MAX913EPA	MAX921CSA
MAX9034AUD+	MAX908ESD+	MAX913EPA+	MAX921CSA+
MAX9038BABT+T	MAX908MJD	MAX913ESA	MAX921CUA
MAX9038BEBT+T	MAX9092AKA+T	MAX913ESA+	MAX921CUA+

Multisim 14.0 Full Components

MAX921EPA	MAX923MJA	MAX933EPA+	MAX942CSA
MAX921EPA+	MAX924CPE	MAX933ESA	MAX942CSA+
MAX921ESA	MAX924CPE+	MAX933ESA+	MAX942CUA+
MAX921ESA+	MAX924CSE	MAX934CPE	MAX942EPA
MAX921MJA	MAX924CSE+	MAX934CPE+	MAX942EPA+
MAX922CPA	MAX924EPE	MAX934CSE	MAX942ESA
MAX922CPA+	MAX924EPE+	MAX934CSE+	MAX942ESA+
MAX922CSA	MAX924ESE	MAX934EPE	MAX942EUA+
MAX922CSA+	MAX924ESE+	MAX934EPE+	MAX942MJA
MAX922CUA+	MAX924MJE	MAX934ESE	MAX944CPD
MAX922EPA	MAX932CPA	MAX934ESE+	MAX944CPD+
MAX922EPA+	MAX932CPA+	MAX941CPA	MAX944CSD
MAX922ESA	MAX932CSA	MAX941CPA+	MAX944CSD+
MAX922ESA+	MAX932CSA+	MAX941CSA	MAX944EPD
MAX922MJA	MAX932CUA+	MAX941CSA+	MAX944EPD+
MAX923CPA	MAX932EPA	MAX941CUA	MAX944ESD
MAX923CPA+	MAX932EPA+	MAX941EPA	MAX944ESD+
MAX923CSA	MAX932ESA	MAX941EPA+	MAX944MJD
MAX923CSA+	MAX932ESA+	MAX941ESA	MAX951EPA+
MAX923CUA	MAX933CPA	MAX941ESA+	MAX951ESA+
MAX923CUA+	MAX933CPA+	MAX941EUA+	MAX951EUA+
MAX923EPA	MAX933CSA	MAX941MJA	MAX951MJA
MAX923EPA+	MAX933CSA+	MAX942AUA+	MAX952EPA
MAX923ESA	MAX933CUA+	MAX942CPA	MAX952EPA+
MAX923ESA+	MAX933EPA	MAX942CPA+	MAX952ESA

Multisim 14.0 Full Components

MAX952ESA+	MAX961ESA	MAX965EUA+	MAX986EXK+
MAX952EUA+	MAX961ESA+	MAX9691EPA+	MAX987ESA+
MAX952MJA	MAX961EUA+	MAX9691ESA+	MAX987EUK+
MAX953EPA	MAX9620AXK+	MAX9691EUA+	MAX987EXK+
MAX953EPA+	MAX9621AUB/V+	MAX9692EPE+	MAX988ESA+
MAX953ESA	MAX9621AUB/V+T	MAX9692ESE+	MAX988EUK+
MAX953ESA+	MAX9621AUB+	MAX9692EUB+	MAX988EXK+
MAX953EUA+	MAX9621AUB+T	MAX9693EEE+	MAX989EKA+
MAX953MJA	MAX962ESA	MAX9693EPE+	MAX989ESA+
MAX954EPA	MAX9636AXT+	MAX9693ESE+	MAX989EUA+
MAX954EPA+	MAX9637AXA+	MAX975ESA+	MAX990EKA+
MAX954ESA	MAX9638AVB+	MAX975EUA+	MAX990ESA+
MAX954ESA+	MAX963ESA	MAX976ESA+	MAX990EUA+
MAX954EUA+	MAX963ESD+	MAX976EUA+	MAX9910EXK+
MAX954MJA	MAX9643TATA+T	MAX976MUA/PR2	MAX9911EWT+
MAX9550EUA+	MAX9643UATA+T	MAX977EEE+	MAX9911EXT+
MAX9550EZK+	MAX9647AUK+T	MAX977ESD+	MAX9912EKA+
MAX9551EUA+	MAX9647AXK+T	MAX978EEE+	MAX9913EUB+
MAX9552EUD+	MAX964ESA	MAX978ESE+	MAX9915EXT+
MAX9600EUP+	MAX9650ATA+	MAX985EBT+T	MAX9916EKA+
MAX9601EUP+	MAX9650AUA+	MAX985ESA+	MAX9917EUB+
MAX9602EUG+	MAX9650AZK+	MAX985EUK+	MAX9918ASA+
MAX9617AXT+	MAX9651ATA+	MAX985EXK+	MAX9919FASA+
MAX9618AXA+	MAX9651AUA+	MAX986ESA+	MAX9919NASA+
MAX9619AXT+	MAX965ESA+	MAX986EUK+	MAX991EKA+

Multisim 14.0 Full Components

MAX991ESA+	MAX9940AXK+	MBR0520LT3G	MBR10H100-E3/45
MAX991EUA+	MAX9943ATT+T	MBR0530	MBR10L60CTG
MAX9920ASA+	MAX9943AUA+	MBR0530T1	MBR1100G
MAX9924UAUB/V+	MAX9944ASA+	MBR0530T1G	MBR1100RLG
MAX9924UAUB/V+ T	MAX9944ATA+T	MBR0530T3G	MBR12035CT
MAX9924UAUB+	MAX994ESD+	MBR0540T1	MBR12045CT
MAX9924UAUB+T	MAX994EUD+	MBR0540T1G	MBR120ESFT1G
MAX9926UAEE/V+	MAX995ESD+	MBR0540T3G	MBR120ESFT3G
MAX9926UAEE/V+T	MAX995EUD+	MBR10100	MBR120LSFT1G
MAX9926UAEE+	MAX996ESD+	MBR10100G	MBR120LSFT3G
MAX9926UAEE+T	MAX996EUD+	MBR10100MFST1G	MBR120VLSFT1G
MAX9928FABT+	MAX997ESA+	MBR10100MFST3G	MBR120VLSFT3G
MAX9928FAUA+	MAX997EUA+	MBR1035	MBR1240MFST1G
MAX9929FABT+	MAX998ESA+	MBR1035G	MBR1240MFST3G
MAX9929FAUA+	MAX998EUT+	MBR1045	MBR130LSFT1G
MAX992EKA+	MAX999AAUK+5	MBR1045G	MBR130T1
MAX992ESA+	MAX999EUK+	MBR1045MFST1G	MBR130T1G
MAX992EUA+	MAXIM-MAXQ-HDR	MBR1045MFST3G	MBR130T3G
MAX9934FART+	MB6S-E3/80	MBR1060	MBR140ESFT1G
MAX9934FAUA+	MBD770DWT1G	MBR1060G	MBR140ESFT3G
MAX9934TART+	MBR030	MBR1080G	MBR140SFT1G
MAX9934TAUA+	MBR040	MBR1090G	MBR140SFT3G
MAX993ESD+	MBR0520L	MBR10H100CTG	MBR150G
MAX993EUD+	MBR0520LT1	MBR10H100CTHE3/ 45	MBR150RLG
	MBR0520LT1G		MBR1520

Multisim 14.0 Full Components

MBR1530	MBR2045CTG	MBR2H100SFT3G	MBR330P
MBR1535CT	MBR2045EMFST1G	MBR30035CT	MBR340
MBR1535CTG	MBR2045EMFST3G	MBR30045CT	MBR340G
MBR1540	MBR2045MFST1G	MBR3020CT	MBR340M
MBR1545CT	MBR2045MFST3G	MBR3035CT	MBR340P
MBR1545CT-E3/45	MBR2060CTG	MBR3035PT	MBR340RLG
MBR1545CTG	MBR2080CTG	MBR3045CT	MBR350RLG
MBR160G	MBR2090CTG	MBR3045PT	MBR3520
MBR160RLG	MBR20H100CT/45	MBR3045PTG	MBR3535
MBR16100CTG	MBR20H100CTG	MBR3045STG	MBR3545
MBR1635	MBR20H150CTG	MBR3045WTG	MBR3545H
MBR1635G	MBR20H200CT-E3/45	MBR30H100CTG	MBR360G
MBR1645	MBR20L45CTG	MBR30H100MFST1G	MBR360RLG
MBR1645G	MBR20L60CTG	MBR30H100MFST3G	MBR4015CTLG
MBR16H45-E3/45	MBR230LSFT1G		MBR4015LWT
MBR1H100SFT3G	MBR2520	MBR30H150CTG	MBR4015LWTG
MBR20035CT	MBR2530	MBR30H30CTG	MBR4020
MBR20045CT	MBR2535CT	MBR30H60CTG	MBR40250G
MBR20100	MBR2535CTG	MBR30L45CTG	MBR40250TG
MBR20100CTG	MBR2535CTL	MBR30L60CTG	MBR4030
MBR20100CTH	MBR2535CTLG	MBR3100G	MBR4040
MBR20200CTG	MBR2540	MBR3100RLG	MBR4045PT-E3/45
MBR2030CTLG	MBR2545CT	MBR320M	MBR4045PTG
MBR2035CT	MBR2545CTG	MBR320P	MBR4045WTG
MBR2045CT		MBR330M	MBR4060PT-E3/45

Multisim 14.0 Full Components

MBR40H100WTG	MBR6045PF	MBRA120ET3G	MBRB20100CTT4
MBR40L45CTG	MBR6045PTG	MBRA130LT3	MBRB20100CTT4G
MBR40L60CTG	MBR6045WTG	MBRA130LT3G	MBRB20200CTG
MBR41H100CTG	MBR60H100CTG	MBRA140T3	MBRB20200CTT4
MBR440MFST1G	MBR60L45CTG	MBRA140T3G	MBRB20200CTT4G
MBR440MFST3G	MBR60L45WTG	MBRA160T3	MBRB2060CTG
MBR460MFST1G	MBR6535	MBRA160T3G	MBRB2060CTT4G
MBR460MFST3G	MBR6545	MBRA1H100T3G	MBRB20H100CTT4 G
MBR5100MFST1G	MBR7030WTL	MBRA210ET3G	MBRB2515LG
MBR5100MFST3G	MBR735	MBRA210LT3G	MBRB2515LT4G
MBR540MFST1G	MBR735G	MBRA2H100T3G	MBRB2535CTLG
MBR540MFST3G	MBR745	MBRA320T3G	MBRB2535CTLT4G
MBR560MFST1G	MBR745-E3/45	MBRA340T3G	MBRB2545CTG
MBR560MFST3G	MBR745G	MBRAF1100T3G	MBRB2545CTT4G
MBR5825	MBR7520	MBRAF1540T3G	MBRB3030CT
MBR5825H	MBR7530	MBRAF2H100T3G	MBRB3030CTG
MBR5831	MBR7535	MBRAF3200T3G	MBRB3030CTL
MBR5831H	MBR7540	MBRAF440T3G	MBRB3030CTLG
MBR5H100MFST1G	MBR7545	MBRB1045G	MBRB3030CTT4G
MBR6035	MBR760-E3/45	MBRB1045T4G	MBRB3045CT-1G
MBR6035B	MBR7H45-E3/45	MBRB1545CTG	MBRB30H30CT-1G
MBR6035PF	MBR8035	MBRB1545CTT4	MBRB30H60CT-1G
MBR6045	MBR8045	MBRB1545CTT4G	MBRB30H60CTT4G
MBR6045B	MBR8H100MFST1G	MBRB1645T4G	MBRB4030
MBR6045H	MBR8H100MFST3G	MBRB20100CTG	

Multisim 14.0 Full Components

MBRB4030G	MBRD360T4	MBRF20L80CTG	MBRM140T3
MBRB4030T4G	MBRD360T4G	MBRF2545CTG	MBRM140T3G
MBRB41H100CT-1G	MBRD5H100T4G	MBRF30H100CTG	MBRM1H100T3G
MBRB41H100CTT4 G	MBRD620CTT4G	MBRF30H150CTG	MBRM2H100T3G
MBRB60H100CTT4 G	MBRD630CTT4G	MBRF30H60CTG	MBRS1100T3
MBRB8H100T4G	MBRD640CTT4	MBRF30L45CTG	MBRS1100T3G
MBRD1035CTL	MBRD640CTT4G	MBRF30L60CTG	MBRS120T3
MBRD1035CTLG	MBRD650CTG	MBRF40250TG	MBRS120T3G
MBRD1035CTLT4G	MBRD650CTT4G	MBRL030	MBRS130LT3
MBRD1045T4G	MBRD660CTG	MBRL040	MBRS130LT3G
MBRD320G	MBRD660CTRLG	MBRM110ET1G	MBRS130T3G
MBRD320RLG	MBRD660CTT4G	MBRM110ET3G	MBRS140T3
MBRD320T4G	MBRD835L	MBRM110LT1G	MBRS140T3G
MBRD330G	MBRD835LG	MBRM110LT3G	MBRS1540T3G
MBRD330RLG	MBRD835LT4G	MBRM120ET1G	MBRS190T3
MBRD330T4G	MBRF10H150CTG	MBRM120ET3G	MBRS190T3G
MBRD340G	MBRF10L60CTG	MBRM120LT1	MBRS2040LT3
MBRD340RLG	MBRF20100CTG	MBRM120LT1G	MBRS2040LT3G
MBRD340T4G	MBRF20200CTG	MBRM120LT3	MBRS230LT3G
MBRD350G	MBRF2045CTG	MBRM120LT3G	MBRS240LT3
MBRD350RLG	MBRF2060CTG	MBRM130LT1G	MBRS240LT3G
MBRD350T4G	MBRF20H100CTG	MBRM130LT3	MBRS260T3G
MBRD360G	MBRF20H150CTG	MBRM130LT3G	MBRS2H100T3G
MBRD360RLG	MBRF20L45CTG	MBRM140T1	MBRS3100T3G
	MBRF20L60CTG	MBRM140T1G	MBRS3200T3

Multisim 14.0 Full Components

MBRS3200T3G	MC1436CU	MC1458U	MC1741SCG
MBRS3201T3G	MC1436D	MC1536G	MC1741SCP1
MBRS320T3	MC1436G	MC1536U	MC1741U
MBRS320T3G	MC1436P1	MC1537L	MC1747CD
MBRS330T3G	MC1436U	MC1539G	MC1747CG
MBRS340T3	MC1437L	MC1556G	MC1747CL
MBRS340T3G	MC1437P	MC1556U	MC1747CP2
MBRS360BT3G	MC1439G	MC1558FK	MC1747G
MBRS360T3	MC1439P1	MC1558G	MC1747L
MBRS360T3G	MC1456CG	MC1558JG	MC1748CG
MBRS410ET3G	MC1456CP1	MC1558SG	MC1748CP1
MBRS410LT3	MC1456G	MC1558SU	MC1748CU
MBRS410LT3G	MC1456P1	MC1558U	MC1748G
MBRS4201T3G	MC1458CD	MC1709AG	MC1748U
MBRS540T3	MC1458CG	MC1709AU	MC1776CD
MBRS540T3G	MC1458CP1	MC1709CG	MC1776CG
MBT2222ADW1T1G	MC1458CU	MC1709CP1	MC1776CP1
MBT35200MT1	MC1458D	MC1709CU	MC1776CU
MBT35200MT1G	MC1458G	MC1709G	MC1776G
MBT3904DW1T1G	MC1458P	MC1741CD	MC1776U
MBT3946DW1T1G	MC1458P1	MC1741CG	MC3301P
MBT3946DW1T2G	MC1458SD	MC1741CP1	MC3302DG
MC1436CD	MC1458SG	MC1741CU	MC3302DR2G
MC1436CG	MC1458SP1	MC1741G	MC3302DTBR2G
MC1436CP1	MC1458SU	MC1741SCD	MC3302PG

Multisim 14.0 Full Components

MC3303D	MC33074ADTBG	MC33079PG	MC33179PG
MC3303L	MC33074ADTBR2G	MC33161DG	MC33181D
MC3303P	MC33074APG	MC33161DMR2G	MC33181P
MC33071ADG	MC33074D	MC33161DR2G	MC33182D
MC33071ADR2G	MC33074DG	MC33161PG	MC33182P
MC33071AP	MC33074DR2G	MC33171D	MC33184D
MC33071APG	MC33074DTBG	MC33171DG	MC33184P
MC33071D	MC33074DTBR2G	MC33171DR2G	MC33272ADG
MC33071DG	MC33074L	MC33171P	MC33272APG
MC33071DR2G	MC33074P	MC33171PG	MC33272D
MC33071P	MC33074PG	MC33172D	MC33272P
MC33071PG	MC33077D	MC33172P	MC33274ADG
MC33071U	MC33077DG	MC33174D	MC33274ADTBR2G
MC33072ADG	MC33077DR2G	MC33174P	MC33274APG
MC33072ADR2G	MC33077P	MC33178D	MC33274D
MC33072AP	MC33077PG	MC33178DG	MC33274P
MC33072APG	MC33078D	MC33178DMR2G	MC33282D
MC33072D	MC33078DG	MC33178DR2G	MC33282P
MC33072DG	MC33078DR2G	MC33178P	MC33284D
MC33072DR2G	MC33078P	MC33178PG	MC33284P
MC33072P	MC33078PG	MC33179D	MC3358P1
MC33072PG	MC33079D	MC33179DG	MC34001D
MC33072U	MC33079DG	MC33179DR2G	MC34001G
MC33074ADG	MC33079DR2G	MC33179DTBR2G	MC34001P
MC33074ADR2G	MC33079P	MC33179P	MC34001U

Multisim 14.0 Full Components

MC3401D	MC3458G	MC4741CD	MCH6534-TL-E
MC3401P	MC3458P1	MC4741CL	MCH6604-TL-E
MC3403D	MC3458U	MC4741CP	MCP6001RT-E/OT
MC3403DG	MC3476G	MC4741L	MCP6001RT-I/OT
MC3403DR2G	MC3476P1	MC68HC11D3CFBL	MCP6001T-E/LT
MC3403L	MC3476U	MC68HC11D3CFN1	MCP6001T-E/OT
MC3403N	MC35001G	MC68HC11D3CP1	MCP6001T-I/LT
MC3403P	MC35001U	MC68HC11E0CFN2	MCP6001T-I/OT
MC3403PG	MC3503L	MC68HC11E1CFN2	MCP6001UT-E/OT
MC3405L	MC3505L	MCH3209-TL-E	MCP6001UT-I/OT
MC3405P	MC35071AU	MCH3377-TL-E	MCP6002-E/MC
MC34071D	MC35071U	MCH3377-TL-H	MCP6002-E/P
MC34071P	MC35080AU	MCH3383-TL-H	MCP6002-I/MS
MC34071U	MC35080U	MCH3474-TL-E	MCP6002-I/P
MC34080D	MC35171U	MCH3474-TL-H	MCP6002-I/SN
MC34080P	MC35181U	MCH3484-TL-H	MCP6002T-E/MS
MC34084DW	MC3558G	MCH6203-TL-E	MCP6002T-E/SN
MC34084P	MC3558U	MCH6320-TL-E	MCP6004-E/P
MC34161DG	MC4558ACP1	MCH6321-TL-E	MCP6004-I/P
MC34161DMR2G	MC4558CD	MCH6336-TL-E	MCP6004-I/SL
MC34161DR2G	MC4558CG	MCH6336-TL-H	MCP6004-I/ST
MC34161PG	MC4558CP1	MCH6337-TL-E	MCP6004T-E/SL
MC34181D	MC4558CU	MCH6337-TL-H	MCP6004T-E/ST
MC34181P	MC4558G	MCH6421-TL-E	MCP601-I/P
MC3458D	MC4558U	MCH6436-TL-E	MCP601-I/SN

Multisim 14.0 Full Components

MCP601-I/ST	MCP6033-E/SN	MCP6051T-E/OT	MCP607-I/SN
MCP601T-I/OT	MCP6034-E/SL	MCP6051T-E/SN	MCP607-I/ST
MCP6021-E/MS	MCP6034-E/ST	MCP6052T-E/MNY	MCP608-I/P
MCP6021-I/P	MCP603T-I/CH	MCP6052T-E/SN	MCP608-I/SN
MCP6021-I/SN	MCP603T-I/P	MCP6054T-E/SL	MCP608-I/ST
MCP6021-I/ST	MCP603T-I/SN	MCP6054T-E/ST	MCP609-I/P
MCP6021T-E/OT	MCP603T-I/ST	MCP6061T-E/MNY	MCP609-I/SL
MCP6022-I/P	MCP6041-I/MS	MCP6061T-E/OT	MCP609-I/ST
MCP6022-I/SN	MCP6041-I/P	MCP6061T-E/SN	MCP6141-I/MS
MCP6022-I/ST	MCP6041-I/SN	MCP6062T-E/MNY	MCP6141-I/P
MCP6023-I/P	MCP6041T-I/OT	MCP6062T-E/SN	MCP6141-I/SN
MCP6023-I/SN	MCP6042-I/MS	MCP6064T-E/SL	MCP6141T-E/OT
MCP6023-I/ST	MCP6042-I/P	MCP6064T-E/ST	MCP6142-I/MS
MCP6024-I/P	MCP6042-I/SN	MCP606-I/P	MCP6142-I/P
MCP6024-I/SL	MCP6043-I/MS	MCP606-I/SN	MCP6142-I/SN
MCP6024-I/ST	MCP6043-I/P	MCP606-I/ST	MCP6143-I/MS
MCP602T-I/P	MCP6043-I/SN	MCP606T-I/OT	MCP6143-I/P
MCP602T-I/SN	MCP6043T-I/CH	MCP6071T-E/MNY	MCP6143-I/SN
MCP602T-I/ST	MCP6044-I/P	MCP6071T-E/OT	MCP6143T-E/CH
MCP6031-E/MS	MCP6044-I/SL	MCP6071T-E/SN	MCP6144-I/P
MCP6031-E/SN	MCP6044-I/ST	MCP6072T-E/MNY	MCP6144-I/SL
MCP6031T-E/OT	MCP604T-I/P	MCP6072T-E/SN	MCP6144-I/ST
MCP6032-E/MS	MCP604T-I/SL	MCP6074T-E/SL	MCP616-I/MS
MCP6032-E/SN	MCP604T-I/ST	MCP6074T-E/ST	MCP616-I/P
MCP6033-E/MS	MCP6051T-E/MNY	MCP607-I/P	MCP616-I/SN

Multisim 14.0 Full Components

MCP617-I/MS	MCP6232T-E/MNY	MCP6271-E/SN	MCP6283-E/MS
MCP617-I/P	MCP6234-E/P	MCP6271RT-E/OT	MCP6283-E/P
MCP617-I/SN	MCP6234-E/SL	MCP6271T-E/OT	MCP6283-E/SN
MCP618-I/MS	MCP6234-E/ST	MCP6272-E/MS	MCP6283T-E/CH
MCP618-I/P	MCP623T-E/CHY	MCP6272-E/P	MCP6284-E/P
MCP618-I/SN	MCP6241-E/MC	MCP6272-E/SN	MCP6284-E/SL
MCP619-I/P	MCP6241-E/MS	MCP6273-E/MS	MCP6284-E/ST
MCP619-I/SL	MCP6241-E/P	MCP6273-E/P	MCP6285-E/MS
MCP619-I/ST	MCP6241-E/SN	MCP6273-E/SN	MCP6285-E/P
MCP621ST-E/OT	MCP6241RT-E/OT	MCP6273T-E/CH	MCP6285-E/SN
MCP621T-E/MNY	MCP6241T-E/OT	MCP6273T-E/SN	MCP6286T-E/OT
MCP621T-E/SN	MCP6241UT-E/LT	MCP6274-E/P	MCP6291-E/MS
MCP622T-E/MF	MCP6241UT-E/OT	MCP6274-E/SL	MCP6291-E/P
MCP622T-E/SN	MCP6242-E/MS	MCP6274-E/ST	MCP6291-E/SN
MCP6231-E/MC	MCP6242-E/P	MCP6275-E/MS	MCP6291RT-E/OT
MCP6231-E/MS	MCP6242-E/SN	MCP6275-E/P	MCP6291T-E/OT
MCP6231-E/P	MCP6244-E/P	MCP6275-E/SN	MCP6292-E/MS
MCP6231-E/SN	MCP6244-E/SL	MCP6281-E/MS	MCP6292-E/P
MCP6231RT-E/OT	MCP6244-E/ST	MCP6281-E/P	MCP6292-E/SN
MCP6231T-E/OT	MCP624T-E/SL	MCP6281-E/SN	MCP6293-E/MS
MCP6231UT-E/LT	MCP624T-E/ST	MCP6281RT-E/OT	MCP6293-E/P
MCP6231UT-E/OT	MCP625T-E/MF	MCP6281T-E/OT	MCP6293-E/SN
MCP6232-E/MS	MCP625T-E/UN	MCP6282-E/MS	MCP6293T-E/CH
MCP6232-E/P	MCP6271-E/MS	MCP6282-E/P	MCP6294-E/P
MCP6232-E/SN	MCP6271-E/P	MCP6282-E/SN	MCP6294-E/SL

Multisim 14.0 Full Components

MCP6294-E/ST	MCP6406T-H/OT	MCP6482-E/MS	MCP653T-E/CHY
MCP6295-E/MS	MCP6407T-H/SN	MCP6482-E/SN	MCP6541-E/P
MCP6295-E/P	MCP6409T-H/SL	MCP6482T-E/MNY	MCP6541-I/MS
MCP6295-E/SN	MCP6421T-E/LTY	MCP6482T-E/MS	MCP6541-I/P
MCP629T-E/ML	MCP6421T-E/OT	MCP6482T-E/SN	MCP6541-I/SN
MCP631T-E/MNY	MCP6441T-E/LT	MCP6484-E/SL	MCP6541RT-E/OT
MCP631T-E/OT	MCP6441T-E/OT	MCP6484-E/ST	MCP6541T-E/MS
MCP631T-E/SN	MCP6442T-E/MNY	MCP6484T-E/SL	MCP6541T-E/OT
MCP632T-E/MF	MCP6442T-E/MS	MCP6484T-E/ST	MCP6541T-E/SN
MCP632T-E/SN	MCP6442T-E/SN	MCP6491T-E/LTY	MCP6541T-I/LT
MCP633T-E/CHY	MCP6444T-E/SL	MCP6491T-E/OT	MCP6541T-I/OT
MCP633T-E/SN	MCP6444T-E/ST	MCP6492-E/MS	MCP6541UT-E/OT
MCP635T-E/MF	MCP6471T-E/LTY	MCP6492-E/SN	MCP6541UT-I/LT
MCP635T-E/UN	MCP6471T-E/OT	MCP6492T-E/MNY	MCP6542-E/P
MCP6401RT-E/OT	MCP6472-E/MS	MCP6492T-E/MS	MCP6542-I/MS
MCP6401T-E/LT	MCP6472-E/SN	MCP6492T-E/SN	MCP6542-I/P
MCP6401T-E/OT	MCP6472T-E/MNY	MCP6494-E/SL	MCP6542-I/SN
MCP6401T-H/OT	MCP6472T-E/MS	MCP6494-E/ST	MCP6542T-E/MS
MCP6401UT-E/OT	MCP6472T-E/SN	MCP6494T-E/SL	MCP6542T-E/SN
MCP6402T-E/MNY	MCP6474-E/SL	MCP6494T-E/ST	MCP6543-E/P
MCP6402T-E/SN	MCP6474-E/ST	MCP651ST-E/OT	MCP6543-I/P
MCP6402T-H/SN	MCP6474T-E/SL	MCP651T-E/MNY	MCP6543-I/SN
MCP6404T-E/SL	MCP6474T-E/ST	MCP651T-E/SN	MCP6543T-E/MS
MCP6404T-E/ST	MCP6481T-E/LTY	MCP652T-E/MF	MCP6543T-E/SN
MCP6404T-H/SL	MCP6481T-E/OT	MCP652T-E/SN	MCP6543T-I/MS

Multisim 14.0 Full Components

MCP6544-E/P	MCP6547T-E/MS	MCP6561T-E/LT	MCP660T-E/ST
MCP6544T-E/SL	MCP6547T-E/SN	MCP6561T-E/OT	MCP661T-E/OT
MCP6544T-E/ST	MCP6547T-I/MS	MCP6561UT-E/OT	MCP661T-E/SN
MCP6544T-I/P	MCP6547T-I/SN	MCP6562T-E/MS	MCP662T-E/MF
MCP6544T-I/SL	MCP6548-E/P	MCP6562T-E/SN	MCP662T-E/MS
MCP6544T-I/ST	MCP6548-I/MS	MCP6564T-E/SL	MCP662T-E/SN
MCP6546-E/P	MCP6548-I/P	MCP6564T-E/ST	MCP663T-E/CHY
MCP6546-I/MS	MCP6548-I/SN	MCP6566RT-E/OT	MCP663T-E/SN
MCP6546-I/P	MCP6548T-E/MS	MCP6566T-E/LT	MCP664T-E/SL
MCP6546-I/SN	MCP6548T-E/SN	MCP6566T-E/OT	MCP664T-E/ST
MCP6546RT-E/OT	MCP6548T-I/MS	MCP6566UT-E/OT	MCP665T-E/MF
MCP6546RT-I/OT	MCP6548T-I/SN	MCP6567T-E/MS	MCP665T-E/UN
MCP6546T-E/MS	MCP6549-E/P	MCP6567T-E/SN	MCP669T-E/ML
MCP6546T-E/OT	MCP6549-I/P	MCP6569T-E/SL	MCP6H01T-E/MNY
MCP6546T-E/SN	MCP6549-I/SL	MCP6569T-E/ST	MCP6H01T-E/SN
MCP6546T-I/LT	MCP6549-I/ST	MCP659T-E/ML	MCP6H02T-E/MNY
MCP6546T-I/MS	MCP6549T-E/SL	MCP65R41T- 1202E/CHY	MCP6H02T-E/SN
MCP6546T-I/OT	MCP6549T-E/ST	MCP65R41T- 2402E/CHY	MCP6H04T-E/SL
MCP6546T-I/SN	MCP6549T-I/SL		MCP6H04T-E/ST
MCP6546UT-E/OT	MCP6549T-I/ST	MCP65R46T- 1202E/CHY	MCP6H71-E/SN
MCP6546UT-I/LT	MCP654T-E/SL		MCP6H71T-E/MNY
MCP6547-E/P	MCP654T-E/ST	MCP65R46T- 2402E/CHY	MCP6H71T-E/SN
MCP6547-I/MS	MCP655T-E/MF	MCP660T-E/ML	MCP6H72-E/SN
MCP6547-I/P	MCP655T-E/UN	MCP660T-E/SL	MCP6H72T-E/MNY
MCP6547-I/SN	MCP6561RT-E/OT		MCP6H72T-E/SN

Multisim 14.0 Full Components

MCP6H74-E/SL	MCP6L02T-E/SN	MCP6L94T-E/SL	MCP6V27T-E/SN
MCP6H74-E/ST	MCP6L04T-E/SL	MCP6L94T-E/ST	MCP6V28T-E/MNY
MCP6H74T-E/SL	MCP6L04T-E/ST	MCP6N11-001E/SN	MCP6V28T-E/MS
MCP6H74T-E/ST	MCP6L1RT-E/OT	MCP6N11T-001E/MNY	MCP6V28T-E/SN
MCP6H81-E/SN	MCP6L1T-E/MS	MCP6V01T-E/MNY	MCP6V31T-E/OT
MCP6H81T-E/MNY	MCP6L1T-E/OT	MCP6V01T-E/SN	MCP6V31UT-E/LT
MCP6H81T-E/SN	MCP6L1T-E/SN	MCP6V02-E/MD	MCP6V31UT-E/OT
MCP6H82-E/SN	MCP6L2T-E/MS	MCP6V02-E/SN	MCR08BT1G
MCP6H82T-E/MNY	MCP6L2T-E/SN	MCP6V03-E/MNY	MCR08MT1G
MCP6H82T-E/SN	MCP6L4T-E/SL	MCP6V03-E/SN	MCR100-3G
MCP6H84-E/SL	MCP6L4T-E/ST	MCP6V06-E/SN	MCR100-3RLG
MCP6H84-E/ST	MCP6L71RT-E/OT	MCP6V06T-E/MNY	MCR1906_2
MCP6H84T-E/SL	MCP6L71T-E/MS	MCP6V07-E/MD	MCR1906_3
MCP6H84T-E/ST	MCP6L71T-E/OT	MCP6V07-E/SN	MCR1906_4
MCP6H91T-E/MNY	MCP6L71T-E/SN	MCP6V08-E/SN	MCR1906_6
MCP6H91T-E/SN	MCP6L72T-E/MS	MCP6V08T-E/MNY	MCR1906_8
MCP6H92T-E/MNY	MCP6L72T-E/SN	MCP6V11T-E/OT	MCR22_2
MCP6H92T-E/SN	MCP6L74T-E/SL	MCP6V11UT-E/LT	MCR22_3
MCP6H94T-E/SL	MCP6L74T-E/ST	MCP6V11UT-E/OT	MCR22_4
MCP6H94T-E/ST	MCP6L91RT-E/OT	MCP6V26T-E/MNY	MCR22_6
MCP6L01RT-E/OT	MCP6L91T-E/MS	MCP6V26T-E/MS	MCR22_8
MCP6L01T-E/LT	MCP6L91T-E/OT	MCP6V26T-E/SN	MCR220_5
MCP6L01T-E/OT	MCP6L91T-E/SN	MCP6V27T-E/MD	MCR220_7
MCP6L01UT-E/OT	MCP6L92T-E/MS	MCP6V27T-E/MS	MCR220_9
MCP6L02T-E/MS	MCP6L92T-E/SN		MCR221_5

Multisim 14.0 Full Components

MCR221_7	MCR3935_7	MDA920A4	MGSF1N03LT1G
MCR221_9	MCR3935_8	MDA920A5	MGSF2N02ELT1G
MCR3818_10	MCR3935_9	MDA920A6	MGW21N60ED
MCR3818_2	MCR703AT4G	MDA920A7	MHD20N06C
MCR3818_3	MCR706AT4G	MDA920A8	MHD20N06G
MCR3818_4	MCR716T4G	MDA920A9	MHD20N06P
MCR3818_6	MCR8SNG	MDA970A1	MICRO_4BIT_ALU
MCR3818_8	MCT6	MDA970A2	MINI-DIN3
MCR3835_1	MDA2500	MDA970A3	MINI-DIN3S
MCR3835_10	MDA2501	MDA970A5	MINI-DIN4
MCR3835_2	MDA2502	MDA970A6	MINI-DIN4S
MCR3835_3	MDA2504	MDA980-1	MINI-DIN5
MCR3835_4	MDA2506	MDA980-2	MINI-DIN5S
MCR3835_5	MDA3500	MDA980-3	MINI-DIN6
MCR3835_6	MDA3501	MDA980-4	MINI-DIN6S
MCR3835_7	MDA3502	MDA980-5	MIPS-EJTAG-HDR
MCR3835_8	MDA3504	MDA980-6	MJ11012G
MCR3835_9	MDA3506	MDA990-1	MJ11015G
MCR3935_1	MDA3508	MDA990-2	MJ11016G
MCR3935_10	MDA3510	MDA990-3	MJ11028G
MCR3935_2	MDA3550	MDA990-4	MJ11032G
MCR3935_3	MDA3551	MDA990-5	MJ11033G
MCR3935_4	MDA920A1	MDA990-6	MJ14002G
MCR3935_5	MDA920A2	MGP11N60ED	MJ15001G
MCR3935_6	MDA920A3	MGSF1N02LT1G	MJ15003G

Multisim 14.0 Full Components

MJ15004G	MJD112RLG	MJD2955G	MJD42CT4G
MJ15015G	MJD112T4G	MJD2955T4G	MJD44E3T4G
MJ15016G	MJD117-1G	MJD3055G	MJD44H11-1G
MJ15022G	MJD117G	MJD3055T4G	MJD44H11G
MJ15023G	MJD117RLG	MJD31C1G	MJD44H11RLG
MJ15024G	MJD117T4G	MJD31CG	MJD44H11T4G
MJ15025G	MJD122G	MJD31CRLG	MJD44H11T5G
MJ21193G	MJD122T4G	MJD31CT4G	MJD45H11-1G
MJ21194G	MJD127G	MJD31T4G	MJD45H11G
MJ21195G	MJD127T4	MJD32CG	MJD45H11RLG
MJ21196G	MJD127T4G	MJD32CRLG	MJD45H11T4G
MJ2955G	MJD148T4	MJD32CT4	MJD47G
MJ4502G	MJD148T4G	MJD32CT4G	MJD47T4G
MJ802G	MJD200G	MJD32RLG	MJD50G
MJB41CG	MJD200RLG	MJD32T4G	MJD50T4G
MJB41CT4G	MJD200T4G	MJD340G	MJD5731T4G
MJB42CT4G	MJD210G	MJD340RLG	MJD6039T4G
MJB44H11G	MJD210RLG	MJD340T4G	MJE13003G
MJB44H11T4	MJD210T4	MJD350G	MJE13005G
MJB44H11T4G	MJD210T4G	MJD350T4G	MJE13007G
MJB45H11G	MJD243G	MJD41CRLG	MJE13009G
MJB45H11T4	MJD243T4G	MJD41CT4G	MJE15028G
MJB45H11T4G	MJD253-1G	MJD42C1G	MJE15029G
MJD112-1G	MJD253T4G	MJD42CG	MJE15030G
MJD112G	MJD2955-1G	MJD42CRLG	MJE15031G

Multisim 14.0 Full Components

MJE15032G	MJE350G	MJF31CG	MM3Z12VT1G
MJE15033G	MJE371G	MJF32CG	MM3Z15VST1G
MJE15034G	MJE4343G	MJF44H11G	MM3Z15VT1G
MJE15035G	MJE4353G	MJF45H11G	MM3Z18VT1G
MJE170G	MJE5730G	MJH11021G	MM3Z20VT1G
MJE171G	MJE5731AG	MJH11022G	MM3Z2V4T1G
MJE172G	MJE5731G	MJH6284G	MM3Z2V7T1G
MJE18002G	MJE5742G	MJH6287G	MM3Z30VT1G
MJE18004G	MJE5850G	MJL1302AG	MM3Z36VT1G
MJE18006G	MJE5851G	MJL21193G	MM3Z39VT1G
MJE18008G	MJE5852G	MJL21194G	MM3Z3V0T1G
MJE180G	MJE700G	MJL21195G	MM3Z3V3ST1G
MJE181G	MJE702G	MJL21196G	MM3Z3V6T1G
MJE182G	MJE703G	MJL3281AG	MM3Z3V9T1G
MJE200G	MJE800G	MJL4281AG	MM3Z43VT1G
MJE210G	MJE802G	MJL4302AG	MM3Z4V3ST1G
MJE243G	MJE803G	MJW18020G	MM3Z4V7T1G
MJE253G	MJF122G	MJW21196G	MM3Z5V1T1G
MJE270G	MJF127G	MJW3281AG	MM3Z5V6ST1G
MJE271G	MJF15030G	MKP3V120G	MM3Z6V8ST1G
MJE2955TG	MJF15031G	MKP3V120RLG	MM3Z8V2ST1G
MJE3055TG	MJF18004G	MKP3V240G	MM5Z10VT1G
MJE340G	MJF18008G	MKP3V240RLG	MM5Z12VT1G
MJE3439G	MJF2955G	MM3Z10VT1G	MM5Z15VT1G
MJE344G	MJF3055G	MM3Z12VST1G	MM5Z16VT1G

Multisim 14.0 Full Components

MM5Z18VT1G	MM5Z7V5T1G	MMBF170LT1G	MMBT4401LT1
MM5Z20VT1G	MM5Z8V2ST1G	MMBF4393LT1G	MMBT4401LT1G
MM5Z24VT1G	MM5Z8V2T1G	MMBF4393LT3G	MMBT4401LT3G
MM5Z27VT1G	MM5Z9V1ST1G	MMBFJ175LT1G	MMBT4401M3T5G
MM5Z2V4ST1G	MM5Z9V1T1G	MMBFJ177LT1G	MMBT4403LT1
MM5Z2V4T1G	MMBD101LT1G	MMBFJ309LT1G	MMBT4403LT1G
MM5Z2V7T1G	MMBD2835LT1G	MMBT2222A	MMBT4403LT3G
MM5Z33VT1G	MMBD2836LT1G	MMBT2222ALT1	MMBT4403M3T5G
MM5Z36VT1G	MMBD2837LT1G	MMBT2222ALT1G	MMBT489LT1G
MM5Z3V0T1G	MMBD2838LT1G	MMBT2222ALT3G	MMBT5401LT1
MM5Z3V3T1G	MMBD301LT1	MMBT2369ALT1G	MMBT5401LT1G
MM5Z3V6T1G	MMBD301LT1G	MMBT2484LT1G	MMBT5401LT3G
MM5Z47VT1G	MMBD301LT3G	MMBT2484LT3G	MMBT5551LT1
MM5Z4V3T1G	MMBD301M3T5G	MMBT2907ALT1	MMBT5551LT1G
MM5Z4V7ST1G	MMBD352LT1G	MMBT2907ALT1G	MMBT5551LT3G
MM5Z4V7ST5G	MMBD353LT1G	MMBT2907ALT3G	MMBT5551M3T5G
MM5Z4V7T1G	MMBD4148	MMBT2907AM3T5 G	MMBT589LT1
MM5Z5V1ST1G	MMBD7000LT1	MMBT3904	MMBT589LT1G
MM5Z5V1T1G	MMBD7000LT1G	MMBT3904LT1	MMBT6428LT1G
MM5Z5V6ST1G	MMBD7000LT3G	MMBT3904LT1G	MMBT6429LT1G
MM5Z5V6T1G	MMBD717LT1G	MMBT3904LT3G	MMBT6517LT1
MM5Z6V2ST1G	MMBD914LT1	MMBT3904TT1G	MMBT6517LT1G
MM5Z6V2T1G	MMBD914LT1G	MMBT3906	MMBT6517LT3G
MM5Z6V8ST1G	MMBD914LT3G	MMBT3906TT1G	MMBT6520LT1
MM5Z6V8T1G	MMBF0201NLT1G		MMBT6520LT1G

Multisim 14.0 Full Components

MMBTA06LT1	MMBZ12VDL	MMBZ5240BLT1G	MMQA5V6T3G
MMBTA06LT1G	MMBZ15VAL	MMBZ5242BLT1G	MMQA6V2T1G
MMBTA06LT3G	MMBZ15VALT1	MMBZ5242BLT3G	MMSD301T1
MMBTA06WT1G	MMBZ15VALT1G	MMBZ5248BLT1G	MMSD301T1G
MMBTA14LT1G	MMBZ15VDL	MMBZ5248BLT3G	MMSD4148T1
MMBTA42	MMBZ15VDLT1G	MMBZ5254BLT1G	MMSD4148T1G
MMBTA42LT1	MMBZ15VDLT3G	MMBZ5256BLT1G	MMSD4148T3G
MMBTA42LT1G	MMBZ18VAL	MMBZ5270BLT1G	MMSF3P02HD
MMBTA42LT3G	MMBZ18VCL	MMBZ5V6AL	MMSZ10T1G
MMBTA56LT1	MMBZ20VAL	MMBZ5V6ALT1G	MMSZ12T1G
MMBTA56LT1G	MMBZ20VALT1G	MMBZ5V6ALT3G	MMSZ2V7T1G
MMBTA56LT3G	MMBZ20VCL	MMBZ6V2AL	MMSZ2V7T3G
MMBTA63LT1G	MMBZ27VAL	MMBZ6V8AL	MMSZ3V3T1G
MMBTA92	MMBZ27VALT1G	MMBZ9V1AL	MMSZ4678T1G
MMBTA92LT1G	MMBZ27VALT3G	MMDL770T1G	MMSZ4679T1G
MMBTA92LT3G	MMBZ27VCL	MMDL914T1	MMSZ4681T1G
MMBTH10-4LT1G	MMBZ27VCLT1G	MMDL914T1G	MMSZ4683T1G
MMBTH10LT1G	MMBZ33VAL	MMDL914T3G	MMSZ4688T1G
MMBTH10LT3G	MMBZ33VALT1G	MMFT960T1G	MMSZ4689T1G
MMBV105GLT1G	MMBZ33VCL	MMG05N60D	MMSZ4689T3G
MMBV3401LT1G	MMBZ5221BLT1G	MMJT350T1G	MMSZ4690T1G
MMBV3401LT3	MMBZ5222BLT1G	MMQA15VT1G	MMSZ4690T3G
MMBV3401LT3G	MMBZ5231BLT1G	MMQA20VT1G	MMSZ4691T1G
MMBZ10VAL	MMBZ5231BLT3G	MMQA20VT3G	MMSZ4692T1G
MMBZ12VAL	MMBZ5232BLT1G	MMQA5V6T1G	MMSZ4696T1G

Multisim 14.0 Full Components

MMSZ4699T1G	MMSZ5258BT3G	MMUN2116LT1G	MOS_P_4T
MMSZ4705T1G	MMSZ5259BT1G	MMUN2130LT1G	MOS_P_4T_DEP
MMSZ4706T1G	MMSZ5260BT1G	MMUN2131LT1G	MOS_P_DEP
MMSZ4707T1G	MMSZ5262BT1G	MMUN2132LT1G	MOTOR_1A
MMSZ4715T1G	MMSZ5263BT1G	MMUN2134LT1G	MOTOR_1C
MMSZ5221BT1G	MMT05B230T3G	MMUN2211LT1G	MOTOR_2A
MMSZ5222BT1G	MMT05B260T3G	MMUN2211LT3G	MOTOR_2C
MMSZ5225BT1G	MMT05B310T3G	MMUN2212LT1G	MOTOR_3A
MMSZ5226BT1G	MMT05B350T3G	MMUN2213LT1G	MOTOR_3C
MMSZ5228BT1G	MMT08B064T3G	MMUN2214LT1G	MOTOR_4A
MMSZ5231BT1G	MMT08B260T3G	MMUN2215LT1G	MOTOR_4C
MMSZ5231BT3G	MMT08B310T3G	MMUN2216LT1G	MOTOR_RATED
MMSZ5234BT1G	MMT08B350T3G	MMUN2231LT1G	MOTOR_VIRTUAL
MMSZ5235BT1G	MMT10B230T3G	MMUN2232LT1G	MPC100AP
MMSZ5235BT3G	MMT10B260T3G	MMUN2233LT1G	MPC100AU
MMSZ5236BT1G	MMT10B310T3G	MMUN2234LT1G	MPC102AP
MMSZ5239BT1G	MMT10B350T3G	MMUN2238LT1G	MPC102AU
MMSZ5240BT1G	MMUN2111LT1G	MMVL3401T1G	MPC104AP
MMSZ5242BT1G	MMUN2111LT3G	MONOSTABLE_VIRTUAL	MPC506AP
MMSZ5242BT3G	MMUN2112LT1G	MOS_N	MPC506AU
MMSZ5243BT1G	MMUN2113LT1G	MOS_N_4T	MPC507AP
MMSZ5245BT1G	MMUN2113LT3G	MOS_N_4T_DEP	MPC507AU
MMSZ5246BT1G	MMUN2114LT1G	MOS_N_DEP	MPC508AP
MMSZ5254BT1G	MMUN2114LT3G	MOS_P	MPC508AU
MMSZ5258BT1G	MMUN2115LT1G		MPC509AP

Multisim 14.0 Full Components

MPC509AU	MPS6513	MPSA06RLRAG	MPSW06G
MPC-BDM-HDR	MPS6514	MPSA06RLRMG	MPSW06RLRAG
MPS2907AG	MPS6515	MPSA06RLRPG	MPSW10
MPS2907ARLG	MPS6516	MPSA10	MPSW42
MPS2907ARLRAG	MPS6517	MPSA18	MPSW45G
MPS2924	MPS6518	MPSA20	MPSW51
MPS2925	MPS6520	MPSA42	MPSW51A
MPS2926	MPS6521	MPSA42G	MPSW51AG
MPS3392	MPS6522	MPSA43	MPSW51ARLRAG
MPS3393	MPS6523	MPSA43G	MPSW51ARLRPG
MPS3395	MPS6531	MPSA55	MPSW51G
MPS3638A	MPS6533	MPSA56	MPSW55
MPS3644	MPS6534	MPSA56G	MPSW56
MPS3646	MPS6562	MPSA56RLRAG	MPZ2012S101A
MPS3702	MPS6565	MPSA56RLRMG	MPZ2012S221A
MPS3703	MPS6566	MPSA56RLRPG	MPZ2012S300A
MPS3704	MPS6571	MPSA56ZL1G	MPZ2012S331A
MPS3707	MPS8098	MPSA70	MPZ3216S500A
MPS3711	MPS8099	MPSA92	MR1120
MPS3826	MPS8598	MPSA93	MR1366
MPS3827	MPSA05	MPSH10	MR1376
MPS3904	MPSA06	MPSL01	MR1386
MPS5172	MPSA06G	MPSL51	MR1396
MPS5179	MPSA06RL1G	MPSW01	MR2400
MPS6512	MPSA06RLG	MPSW01A	MR2400F

Multisim 14.0 Full Components

MR2401	MR5030	MR824	MRA4005T3G
MR2401F	MR504	MR826	MRA4006T3G
MR2402	MR5040	MR830	MRA4007T3G
MR2402F	MR5059	MR831	MRF5711LT1
MR2404	MR506	MR832	MRF5812
MR2404F	MR5060	MR834	MRF9011LT1
MR2406	MR5061	MR836	MRF9011LT1_A
MR2406F	MR508	MR850	MRF9011LT1_B
MR2500	MR510	MR851	MRF9411LT1
MR2501	MR750	MR852	MRF947T1
MR2502	MR751	MR854	MRF9511LT1
MR2504	MR752	MR856	MRS1504T3G
MR2506	MR754	MR860	MSB92T1G
MR2508	MR756	MR861	MSD1328-RT1G
MR2510	MR810	MR862	MSD602-RT1G
MR327	MR811	MR864	MSE1PJHM3/89A
MR328	MR812	MR866	MSP3V3HM3/89A
MR330	MR813	MR870	MSP430P325IFN
MR331	MR814	MR871	MSP430P325IPG
MR500	MR816	MR872	MSP430P325IPM
MR5005	MR817	MR874	MSQA6V1W5T2G
MR501	MR818	MR876	MSR1560G
MR5010	MR820	MRA4003T3G	MSR860G
MR502	MR821	MRA4004T3G	MSRD620CTG
MR5020	MR822	MRA4005T1G	MSRD620CTRG

Multisim 14.0 Full Components

MSRD620CTT4	MTH30N20	MTP40N06M	MUN2214T1G
MSRD620CTT4G	MTH5N100	MTP4N50	MUN2214T3G
MSRD620CTT4RG	MTH8N60	MTP4N85	MUN2215T1G
MSRF1560G	MTM10N100E	MTP50N05EL	MUN2216T1G
MSRF860G	MTM15N40	MTP50N06E	MUN2230T1G
MSS1P3LHM3/89A	MTM24N50E	MTP6N60	MUN2232T1G
MSS1P4HM3/89A	MTM26N40E	MTP6N60/MC	MUN2233T1G
MSS1P6HM3/89A	MTM8N60	MTP7N20	MUN2234T1G
MSS2P3HM3/89A	MTP10N05E/MC	MTP8N50E	MUN2236T1G
MTB20N20E	MTP12P10	MTP8P10	MUN2237T1G
MTB50P03HDLT4G	MTP15N05E	MULTIPLIER	MUN2238T1G
MTD10P06HDL	MTP15N06E	MUN2111T1G	MUN2240T1G
MTD15N06V	MTP20P06	MUN2112T1G	MUN5111DW1T1G
MTD1N60E	MTP25N06	MUN2113T1G	MUN5111T1G
MTD1N80E	MTP25N06L	MUN2114T1G	MUN5112DW1T1G
MTD2955E	MTP25N10E	MUN2115T1G	MUN5112T1G
MTD2N50E	MTP2N50	MUN2135T1G	MUN5113DW1T1G
MTD3055V	MTP2P50	MUN2138T1G	MUN5113T1G
MTD3055VL	MTP2P50EG	MUN2141T1G	MUN5113T3G
MTD4N20E	MTP3055E/MC	MUN2211T1	MUN5114DW1T1G
MTD4P06	MTP3055V	MUN2211T1G	MUN5114T1G
MTD5N06	MTP3055VL	MUN2211T3G	MUN5115DW1T1G
MTD6N15T4G	MTP30N08M	MUN2212T1G	MUN5115T1G
MTD6N20ET4G	MTP35N06E	MUN2213T1	MUN5116DW1T1G
MTH13N50	MTP3N100	MUN2213T1G	MUN5131T1G

Multisim 14.0 Full Components

MUN5132T1G	MUN5235DW1T1G	MUR110	MUR1560
MUN5133DW1T1G	MUN5237DW1T1G	MUR1100EG	MUR1560G
MUN5133T1G	MUN5238T1G	MUR1100ERLG	MUR160
MUN5135DW1T1G	MUN5240T1G	MUR110G	MUR1605CT
MUN5135T1G	MUN5241T1G	MUR110RLG	MUR160G
MUN5140T1G	MUN5311DW1T1G	MUR115	MUR160RLG
MUN5211DW1T1G	MUN5312DW1T1G	MUR115G	MUR1610CT
MUN5211T1	MUN5312DW1T2G	MUR115RLG	MUR1610CTG
MUN5211T1G	MUN5313DW1T1G	MUR120G	MUR1615CT
MUN5212DW1T1G	MUN5314DW1T1G	MUR120RLG	MUR1615CTG
MUN5212T1G	MUN5315DW1T1G	MUR130G	MUR1620CT
MUN5213DW1T1G	MUN5316DW1T1G	MUR130RLG	MUR1620CTG
MUN5213DW1T3G	MUN5330DW1T1G	MUR140G	MUR1620CTRG
MUN5213T1G	MUN5333DW1T1G	MUR140RLG	MUR1640CTG
MUN5214DW1T1G	MUN5334DW1T1G	MUR1505	MUR1660CTG
MUN5214T1G	MUN5335DW1T1G	MUR1510	MUR180EG
MUN5215DW1T1G	MUN5336DW1T1G	MUR1510G	MUR180ERLG
MUN5215T1G	MUR10005CT	MUR1515	MUR2020RG
MUN5216DW1T1G	MUR10010CT	MUR1515G	MUR2100EG
MUN5230DW1T1G	MUR10015CT	MUR1520	MUR2100ERLG
MUN5230T1G	MUR10020CT	MUR1520G	MUR210G
MUN5232DW1T1G	MUR10150E	MUR1530	MUR210RLG
MUN5232T1G	MUR105	MUR1540	MUR220G
MUN5233DW1T1G	MUR105G	MUR1540G	MUR220RLG
MUN5233T1G	MUR105RLG	MUR1550	MUR240G

Multisim 14.0 Full Components

MUR240RLG	MUR415RLG	MUR810G	MURA215T3
MUR2505	MUR420	MUR815	MURA215T3G
MUR2510	MUR420G	MUR815G	MURA220T3
MUR2515	MUR420RLG	MUR820	MURA220T3G
MUR2520	MUR440G	MUR820G	MURA230T3G
MUR260G	MUR440RLG	MUR830	MURA240T3G
MUR260RLG	MUR460G	MUR840	MURB1620CTG
MUR3005PT	MUR460RLG	MUR840G	MURB1620CTRG
MUR3010PT	MUR480EG	MUR850	MURB1620CTRT4G
MUR3015PT	MUR480ERLG	MUR860	MURB1620CTT4
MUR3020PT	MUR5005	MUR860G	MURB1620CTT4G
MUR3020PTG	MUR5010	MUR880EG	MURB1660CTG
MUR3020WTG	MUR5015	MURA105T3G	MURB1660CTT4G
MUR3040PTG	MUR5020	MURA110T3	MURD320T4
MUR3060PTG	MUR550APFRLG	MURA110T3G	MURD320T4G
MUR3060WTG	MUR550PFG	MURA115T3G	MURD330T4G
MUR405	MUR605CT	MURA120T3	MURD340T4G
MUR405G	MUR610CT	MURA120T3G	MURD530T4G
MUR410	MUR615CT	MURA130T3G	MURD550PFT4G
MUR4100EG	MUR620CT	MURA140T3	MURD620CT
MUR4100ERLG	MUR620CTG	MURA140T3G	MURD620CTG
MUR410G	MUR805	MURA160T3	MURD620CTT4
MUR410RLG	MUR805G	MURA160T3G	MURD620CTT4G
MUR415	MUR810	MURA205T3G	MURF1560G
MUR415G	MUR8100EG	MURA210T3G	MURF1620CTG

Multisim 14.0 Full Components

MURF1660CTG	MURS205T3G	MUX2_1INV_3S	MZ4626
MURF550PFG	MURS210T3G	MUX4_1	MZ4627
MURF860G	MURS220T3	MUX4_1_INVO	MZ5520B
MURH840CTG	MURS220T3G	MUX8_1	MZ5521B
MURH860CTG	MURS230T3	MVGSF1N03LT1G	MZ5522B
MURHB840CTG	MURS230T3G	MVMBF0201NLT1G	MZ5523B
MURHB840CTT4	MURS240T3G	myRIO_MXP	MZ5524B
MURHB840CTT4G	MURS310T3	MZ4099	MZ5525B
MURHB860CTT4G	MURS320T3	MZ4100	MZ5526B
MURHD560T4G	MURS320T3G	MZ4101	MZ5527B
MURHD560W1T4G	MURS340T3	MZ4102	MZ5528B
MURHF860CTG	MURS340T3G	MZ4103	MZ5529B
MURHS160T3G	MURS360BT3G	MZ4104	MZ5530B
MURS105T3G	MURS360-E3/57T	MZ4614	MZPY10
MURS110T3	MURS360T3	MZ4615	MZPY100
MURS110T3G	MURS360T3G	MZ4616	MZPY11
MURS115T3	MURS480ET3G	MZ4617	MZPY12
MURS115T3G	MUSHROOM_HEAD	MZ4618	MZPY13
MURS120T3	MUX_16TO1	MZ4619	MZPY15
MURS120T3G	MUX_2TO1	MZ4620	MZPY16
MURS140T3	MUX_4TO1	MZ4621	MZPY18
MURS140T3G	MUX_8TO1	MZ4622	MZPY20
MURS160-E3/52T	MUX_LATCH	MZ4623	MZPY22
MURS160T3	MUX2_1	MZ4624	MZPY24
MURS160T3G	MUX2_1_INV	MZ4625	MZPY27

Multisim 14.0 Full Components

MZPY3.9	N83C196KB	NCP1117DT15RKG	NCP1117ST33T3G
MZPY30	N87C196KB	NCP1117DT18G	NCP1117ST50T3G
MZPY33	NAND13	NCP1117DT18RKG	NCP1117STAT3G
MZPY36	NAND2	NCP1117DT18T5G	NCP511SN15T1G
MZPY39	NAND2	NCP1117DT20G	NCP511SN18T1G
MZPY4.3	NAND3	NCP1117DT20RKG	NCP511SN25T1G
MZPY4.7	NAND3	NCP1117DT25G	NCP511SN27T1G
MZPY43	NAND4	NCP1117DT25RKG	NCP511SN28T1G
MZPY47	NAND4	NCP1117DT25T5G	NCP511SN30T1G
MZPY5.1	NAND5	NCP1117DT285G	NCP511SN33T1G
MZPY5.6	NAND5	NCP1117DT285RKG	NCP511SN50T1G
MZPY51	NAND6	NCP1117DT33G	NCP5355D
MZPY56	NAND6	NCP1117DT33RKG	NCP5355DG
MZPY6.2	NAND7	NCP1117DT33T5G	NCP5355PDR2
MZPY6.8	NAND7	NCP1117DT50G	NCS2001SN1T1G
MZPY62	NAND8	NCP1117DT50RKG	NCS2001SN2T1G
MZPY68	NAND8	NCP1117DTAG	NCS2001SQ1T2G
MZPY7.5	NBRB8H100T4G	NCP1117DTARKG	NCS2001SQ2T2G
MZPY75	NBRD5H100T4G	NCP1117DTAT5G	NCS2200SN1T1G
MZPY8.2	NBR52H100T3G	NCP1117ST12T3G	NCS2200SN2T1G
MZPY82	NC_CONTACT	NCP1117ST15T3G	NCS2200SQ2T2G
MZPY9.1	NC_RELAY_RATED	NCP1117ST18T3G	NCS2200SQLT1G
MZPY91	NCP1117DT12G	NCP1117ST20T3G	NCS2202SN1T1G
N2550-6002RB	NCP1117DT12RKG	NCP1117ST25T3G	NCS2202SN2T1G
N80C196KB	NCP1117DT15G	NCP1117ST285T3G	NCS2202SQ1T2G

Multisim 14.0 Full Components

NCS2202SQ2T2G	NCV2904DMR2G	NDD60N360U1-1G	NDF9407
NCV1117DT15RKG	NCV2904DR2G	NDD60N360U1-35G	NDF9409
NCV1117DT18RKG	NCV33074ADTBR2 G	NDD60N360U1T4G	NDF9410
NCV1117DT18T5G	NCV33074DR2G	NDF02N60ZG	NDS8852H
NCV1117DT20RKG	NCV33272ADR2G	NDF02N60ZH	NDS8858H
NCV1117DT25RKG	NCV833DR2G	NDF03N60ZG	NDS8936
NCV1117DT33T5G	NDD01N60-1G	NDF03N60ZH	NDS8947
NCV1117DT50RKG	NDD01N60T4G	NDF04N60ZG	NDS9936
NCV1117DTARKG	NDD02N40-1G	NDF04N60ZH	NDS9942
NCV1117ST12T3G	NDD02N40T4G	NDF04N62ZG	NDS9943
NCV1117ST15T3G	NDD02N60Z-1G	NDF05N50ZG	NDS9947
NCV1117ST18T3G	NDD02N60ZT4G	NDF05N50ZH	NDS9948
NCV1117ST20T3G	NDD03N50Z-1G	NDF06N60ZG	NDS9952
NCV1117ST25T3G	NDD03N50ZT4G	NDF06N60ZH	NDS9952A
NCV1117ST33T3G	NDD03N60Z-1G	NDF06N62ZG	NDS9953
NCV1117ST50T3G	NDD03N60ZT4G	NDF08N50ZG	NDS9953A
NCV1117STAT3G	NDD03N80Z-1G	NDF08N50ZH	NDS9955
NCV2001SN2T1G	NDD03N80ZT4G	NDF08N60ZG	NDS9956A
NCV2001SQ2T2G	NDD04N50Z-1G	NDF08N60ZH	NDS9958
NCV2901DR2G	NDD04N50ZT4G	NDF10N60ZG	NDS9959
NCV2901DTBR2G	NDD04N60Z-1G	NDF10N60ZH	NDT01N60T1G
NCV2902DR2G	NDD04N60ZT4G	NDF10N62ZG	NE5532AI
NCV2902DTBR2G	NDD05N50Z-1G	NDF11N50ZG	NE5532AIP
NCV2903DMR2G	NDD05N50ZT4G	NDF11N50ZH	NE5532AP
NCV2903DR2G		NDF9406	NE5532IP

Multisim 14.0 Full Components

NE5532P	NGTB15N60S1EG	NI_sbRIO_J7_CONN	NI-9683_LVTTL
NE5534AD	NGTB50N60FLWG	NI_sbRIO_J7_PORT S	NI-AT-GPIB/TNT
NE5534AP	NHPJ08S600G		NID9N05CLT4G
NE5534D	NHPJ15S600G	NI_sbRIO_P2_CON N	NI-DAQCard-6024E
NE5534P	NHPV08S600G	NI_sbRIO_P2_PORT S	NI-DAQCard-6036E
NET_10	NHPV15S600G		NI-DAQCard-6062E
NET_12	NI_2VHDCI_68_68_ RA	NI_sbRIO_P3_CON N	NI-DAQPad- 6015(Mass.Term.)
NET_14			
NET_16	NI_50MIL_68_RA	NI_sbRIO_P3_PORT S	NI-DAQPad-6020E
NET_18	NI_50MIL_68_V		NI-DAQPad-6052E
NET_2	NI_cRIO_4LED_RA	NI_sbRIO_P4_CON N	NI-ExpressCard- GPIB
NET_20	NI_cRIO_BNC	NI_sbRIO_P4_PORT S	NIF9N05CLT1G
NET_3	NI_cRIO_DSUB25M		
NET_4	NI_cRIO_DSUB37M	NI_sbRIO_P5_CON N	NIF9N05CLT3G
NET_6	NI_cRIO_INTERFAC E_GENERIC	NI_sbRIO_P5_PORT S	NI-GPIB-ENET/100
NET_8	NI_cRIO_INTERFAC E_ID		NI-GPIB-ENET/1000
NF5101		NI_VHDCI_68_RA	NI-GPIB-PCII/IIA
NF5102	NI_cRIO_INTERFAC E_PARALLEL	NI_VHDCI_68_V	NI-GPIB-RS232
NF5103		NI-78xxR_RDIO	NI-GPIB-RS485/422
NF5301	NI_cRIO_INTERFAC E_SPI	NI-9683_AI	NI-GPIB-USB-HS
		NI-9683_AIO	NI-myDAQ
NGB18N40CLBT4G	NI_cRIO_INTERFAC E_USER	NI-9683_DI	NI-PCI-6011E
NGB8207NT4G		NI-9683_DO	NI-PCI-6013
NGD15N41CLT4G	NI_cRIO_SCREWTE RM10	NI-	NI-PCI-6014
NGD18N40CLBT4G	NI_sbRIO_J5_CONN	9683_HALFBRIDGE_ DO	NI-PCI-6023E
NGD8201NT4G	NI_sbRIO_J6_CONN		NI-PCI-6024E

Multisim 14.0 Full Components

NI-PCI-6030E	NI-PCI-6232	NI-PCle-6323	NI-PXI-6052E
NI-PCI-6032E	NI-PCI-6233	NI-PCle-6341	NI-PXI-6070E
NI-PCI-6034E	NI-PCI-6236	NI-PCle-6343	NI-PXI-6115
NI-PCI-6035E	NI-PCI-6238	NI-PCle-6351	NI-PXI-6120
NI-PCI-6036E	NI-PCI-6239	NI-PCle-6353	NI-PXI-6122
NI-PCI-6040E	NI-PCI-6250	NI-PCle-6361	NI-PXI-6123
NI-PCI-6052E	NI-PCI-6254	NI-PCle-6363	NI-PXI-6132
NI-PCI-6070E	NI-PCI-6255	NI-PCle- 7841R_RMIO	NI-PXI-6133
NI-PCI-6110	NI-PCI-6259		NI-PXI-6143
NI-PCI-6111	NI-PCI-6280	NI-PCle- 7842R_RMIO	NI-PXI-6221
NI-PCI-6115	NI-PCI-6281	NI-PCle- 7851R_RMIO	NI-PXI-6224
NI-PCI-6120	NI-PCI-6284		NI-PXI-6225
NI-PCI-6122	NI-PCI-6289	NI-PCle- 7852R_RMIO	NI-PXI-6229
NI-PCI-6123	NI-PCI-7811R	NI-PCle-GPIB	NI-PXI-6230
NI-PCI-6132	NI-PCI-7813R	NI-PCle-GPIB/LP	NI-PXI-6232
NI-PCI-6133	NI-PCI- 7830R_RMIO	NI-PCle-GPIB+	NI-PXI-6233
NI-PCI-6143		NI-PCle-GPIB+/LP	NI-PXI-6236
NI-PCI-6154	NI-PCI- 7831R_RMIO	NI-PCI-GPIB	NI-PXI-6238
NI-PCI-6220	NI-PCI- 7833R_RMIO	NI-PCI-GPIB/LP	NI-PXI-6239
NI-PCI-6221		NI-PCI-GPIB+	NI-PXI-6250
NI-PCI-6221(37-Pin)	NI-PCI-8232	NI-PCMCIA-GPIB	NI-PXI-6251
NI-PCI-6224	NI-PCle-6251	NI-PMC-GPIB	NI-PXI-6254
NI-PCI-6225	NI-PCle-6259		NI-PXI-6255
NI-PCI-6229	NI-PCle-6320	NI-PXI-6030E	NI-PXI-6259
NI-PCI-6230	NI-PCle-6321	NI-PXI-6040E	NI-PXI-6280

Multisim 14.0 Full Components

NI-PXI-6281	NI-sbRIO-9606	NI-USB-6251(Mass.Term.)	NJL4302D
NI-PXI-6284	NI-sbRIO-9651		NJL4302DG
NI-PXI-6289	NI-SCXI-1127_1-Wire	NI-USB-6255(Mass.Term.)	NJM022BD
NI-PXI-7811R		NI-USB-6259(Mass.Term.)	NJM022BL
NI-PXI-7813R	NI-SCXI-1127_2-Wire		NJM022BM
NI-PXI-7830R_RMIO	NI-SCXI-1127_4-Wire	NI-USB-6281(Mass.Term.)	NJM022D
NI-PXI-7831R_RMIO			NJM022L
NI-PXI-7833R_RMIO	NI-SCXI-1127_Independent	NI-USB-6289(Mass.Term.)	NJM022M
NI-PXI-7841R_RMIO	NI-SCXI-1127_Matrix	NI-USB-7845R_MIO	NJM062D
NI-PXI-7842R_RMIO		NI-USB-7846R_MIO	NJM062L
NI-PXI-7851R_RMIO	NI-SCXI-1128_1-Wire	NI-USB-7855R_MIO	NJM062M
NI-PXI-7852R_RMIO		NI-USB-7856R_MIO	NJM062V
NI-PXI-7853R_RMIO	NI-SCXI-1128_2-Wire	NI-USB-78xxR_DIO	NJM064D
NI-PXI-7854R_RMIO	NI-SCXI-1128_4-Wire	NJD1718T4G	NJM064M
NI-PXI-8232		NJD2873T4G	NJM064V
NI-PXIe-6124	NI-SCXI-1128_Independent	NJD35N04G	NJM072BD
NI-PXIe-6341	NI-SCXI-1128_Matrix	NJD35N04T4G	NJM072BL
NI-PXIe-6356		NJL0281D	NJM072BM
NI-PXIe-6358	NI-SCXI-1160	NJL0281DG	NJM072BV
NI-PXIe-6361	NI-SCXI-1163R	NJL0302D	NJM072D
NI-PXIe-6363	NI-USB-6212(Mass.Term.)	NJL0302DG	NJM072L
NI-PXIe-6366		NJL1302DG	NJM072M
NI-PXIe-6368	NI-USB-6216(Mass.Term.)	NJL3281DG	NJM074D
NI-PXI-GPIB	NI-USB-6225(Mass.Term.)	NJL4281D	NJM074M
NI-sbRIO-9605		NJL4281DG	NJM074V

Multisim 14.0 Full Components

NJM082BD	NJM2059M	NJM2121M	NJM3415M
NJM082BL	NJM2060D	NJM2900M	NJM3416V
NJM082BM	NJM2060M	NJM2900N	NJM353D
NJM082BV	NJM2068D	NJM2902M	NJM353M
NJM082D	NJM2068L	NJM2902N	NJM3900M
NJM082L	NJM2068M	NJM2902V	NJM3900N
NJM082V	NJM2082D	NJM2904D	NJM4250D
NJM084D	NJM2082L	NJM2904L	NJM4250M
NJM084M	NJM2082M	NJM2904M	NJM4565D
NJM084V	NJM2097M	NJM2904V	NJM4565L
NJM13600D	NJM2100D	NJM318D	NJM4565M
NJM13600M	NJM2100L	NJM318M	NJM4565V
NJM13700D	NJM2100M	NJM324D	NJM4580D
NJM13700M	NJM2100V	NJM324M	NJM4580E
NJM1458D	NJM2107F	NJM3403AD	NJM4580L
NJM1458M	NJM2114D	NJM3403AM	NJM4741D
NJM2041D	NJM2114L	NJM3403AV	NJM4741M
NJM2041L	NJM2115D	NJM3404AD	NJM5532D
NJM2041M	NJM2115L	NJM3404AL	NJM5532L
NJM2043D	NJM2115M	NJM3404AM	NJM5532M
NJM2043L	NJM2120D	NJM3414D	NJM5534D
NJM2043M	NJM2120L	NJM3414L	NJM5534M
NJM2058D	NJM2120M	NJM3414M	NJM741D
NJM2058M	NJM2121D	NJM3415D	NJM741E
NJM2059D	NJM2121L	NJM3415L	NJM741M

Multisim 14.0 Full Components

NJMOP-07D	NJVMJD350T4G	NON_IDEAL_BATTE RY	NPD5564
NJMOP-07M	NJVMJD42CRLG		NPD5565
NJT4030PT1G	NJVMJD42CT4G	NON_IDEAL_CAPAC ITOR	NPD5566
NJT4030PT3G	NJVMJD44E3T4G	NON_IDEAL_INDUC TOR	NPD8301
NJT4031NT1G	NJVMJD44H11G		NPD8303
NJT4031NT3G	NJVMJD44H11RLG	NON_IDEAL_RESIST OR	NRVA4004T3G
NJV4030PT1G	NJVMJD44H11T4G		NRVB0530T1G
NJV4030PT3G	NJVMJD45H11RLG	NONC_RELAY_RATE D	NRVB0530T3G
NJV4031NT1G	NJVMJD45H11T4G	NONLINEAR_DEPEN DENT	NRVB0540T1G
NJV4031NT3G	NJVMJD50T4G		NRVB0540T3G
NJVMJB41CT4G	NJVMJD6039T4G	NOR2	NRVB10100G
NJVMJB42CT4G	NJVNJD2873T4G	NOR2	NRVB10100MFST1 G
NJVMJB44H11T4G	NJVNJD35N04G	NOR3	NRVB10100MFST3 G
NJVMJB45H11T4G	NJVNJD35N04T4G	NOR3	
NJVMJD112T4G	NJW0281G	NOR4	NRVB1045MFST1G
NJVMJD117T4G	NJW0302G	NOR4	NRVB1045MFST3G
NJVMJD210T4G	NJW1302G	NOR5	NRVB120ESFT1G
NJVMJD243T4G	NJW21193G	NOR5	NRVB120ESFT3G
NJVMJD253T4G	NJW21194G	NOR6	NRVB120LSFT1G
NJVMJD2955T4G	NJW3281G	NOR6	NRVB1240MFST1G
NJVMJD3055T4G	NJX1675PDR2G	NOR7	NRVB1240MFST3G
NJVMJD31T4G	NLT_VIRTUAL	NOR7	NRVB130T1G
NJVMJD32CG	NMOSFET_Thermal	NOR8	NRVB140ESFT1G
NJVMJD32CT4G	NO_CONTACT	NOR8	NRVB140ESFT3G
NJVMJD32T4G	NO_RELAY_RATED	NOT	NRVB140SFT1G

Multisim 14.0 Full Components

NRVB140SFT3G	NRVB8H100MFST1 G	NRVBD640CTT4G	NRVUB1620CTT4G
NRVB1H100SFT3G		NRVBD650CTT4G	NRVUB1660CTT4G
NRVB2045EMFST1 G	NRVB8H100MFST3 G	NRVBD660CTG	NRVUD550PFT4G
NRVB2045EMFST3 G	NRVBA130LT3G	NRVBD660CTT4G	NRVUD620CTG
	NRVBA160T3G	NRVBM110ET1G	NRVUD620CTT4G
NRVB2H100SFT3G	NRVBA1H100T3G	NRVBM110LT1G	NRVUS230T3G
NRVB30H100MFST 1G	NRVBA210LT3G	NRVBM110LT3G	NRVUS240T3G
NRVB30H100MFST 3G	NRVBA2H100T3G	NRVBM120ET1G	NS32FV16-20
	NRVBA340T3G	NRVBM120ET3G	NS32FV16-25
NRVB440MFST1G	NRVBB1060T4G	NRVBM130LT1G	NS32FX161-15
NRVB440MFST3G	NRVBB20100CTT4G	NRVBM130LT3G	NS32FX161-20
NRVB440MFSWFT1 G	NRVBB2060CTT4G	NRVBM140T1G	NS32FX164-20
NRVB440MFSWFT3 G	NRVBB20H100CTT4 G	NRVBM140T3G	NS32FX164-25
	NRVBB2535CTLG	NRVBS2040LT3G	NSA5.0AT3G
NRVB460MFST1G	NRVBB2535CTLT4G	NRVBS240LT3G	NSB12ANT3G
NRVB460MFST3G	NRVBB3030CTLG	NRVBS260T3G	NSB4904DW1T1G
NRVB5100MFST1G	NRVBB3030CTLT4G	NRVBS3100T3G	NSB8MT-E3/81
NRVB5100MFST3G	NRVBB30H60CTT4G	NRVBS3200T3G	NSB9435T1G
NRVB540MFST1G	NRVBB4030T4G	NRVBS3201T3G	NSBA114EDP6T5G
NRVB540MFST3G	NRVBB41H100CTT4 G	NRVBS330T3G	NSBA114EDXV6T1G
NRVB560MFST1G		NRVBS360T3G	NSBA114EF3T5G
NRVB560MFST3G	NRVBBS20100CTT4 G	NRVBS4201T3G	NSBA114TDP6T5G
NRVB5H100MFST1 G	NRVBD1035CTLT4G	NRVBS540T3G	NSBA114TF3T5G
	NRVBD640CTG	NRVS1504T3G	NSBA114YDP6T5G
		NRVUB1620CTRT4G	NSBA114YDXV6T1G

Multisim 14.0 Full Components

NSBA115EDXV6T1G	NSBC114EDXV6T1G	NSBC123JF3T5G	NSBC144EF3T5G
NSBA115TDP6T5G	NSBC114EDXV6T5G	NSBC123JPDP6T5G	NSBC144EPDP6T5G
NSBA115TF3T5G	NSBC114EF3T5G	NSBC123JPDXV6T1G	NSBC144EPDXV6T1G
NSBA123EF3T5G	NSBC114EPDP6T5G	NSBC123TDP6T5G	NSBC144TF3T5G
NSBA123JDP6T5G	NSBC114EPDXV6T1G	NSBC123TF3T5G	NSBC144WDP6T5G
NSBA123JDXV6T5G	NSBC114EPDXV6T5G	NSBC124EDP6T5G	NSBC144WF3T5G
NSBA123JF3T5G	NSBC114TDP6T5G	NSBC124EDXV6T1G	NSD16F3T5G
NSBA123TDP6T5G	NSBC114TDXV6T1G	NSBC124EF3T5G	NSD914F3T5G
NSBA123TF3T5G	NSBC114TF3T5G	NSBC124EPDXV6T1G	NSDEMP11XV6T1G
NSBA124EDP6T5G	NSBC114YDP6T5G	NSBC124XF3T5G	NSDEMP11XV6T5G
NSBA124EF3T5G	NSBC114YDXV6T1G	NSBC143EDP6T5G	NSL12AWT1G
NSBA124XF3T5G	NSBC114YDXV6T5G	NSBC143EF3T5G	NSM80100MT1G
NSBA143EDP6T5G	NSBC114YF3T5G	NSBC143TF3T5G	NSM80101MT1G
NSBA143EF3T5G	NSBC114YPDP6T5G	NSBC143TPDXV6T1G	NSR0130P2T5G
NSBA143TF3T5G	NSBC114YPDXV6T1G	NSBC143ZDP6T5G	NSR0140P2T5G
NSBA143ZDP6T5G	NSBC114YPDXV6T5G	NSBC143ZDXV6T1G	NSR01F30MXT5G
NSBA143ZF3T5G	NSBC115EDXV6T1G	NSBC143ZF3T5G	NSR01F30NXT5G
NSBA144EDP6T5G	NSBC115TDP6T5G	NSBC143ZPDP6T5G	NSR01L30MXT5G
NSBA144EDXV6T1G	NSBC115TF3T5G	NSBC143ZPDXV6T1G	NSR01L30NXT5G
NSBA144EF3T5G	NSBC115TPDP6T5G	NSBC144EDP6T5G	NSR0230P2T5G
NSBA144TF3T5G	NSBC123EF3T5G	NSBC144EDXV6T1G	NSR0240HT1G
NSBA144WDP6T5G	NSBC123JDP6T5G	NSBC144EDXV6T5G	NSR0240P2T5G
NSBA144WF3T5G			NSR0240V2T1G
NSBC113EF3T5G			NSR02F30NXT5G
NSBC114EDP6T5G			

Multisim 14.0 Full Components

NSR02L30NXT5G	NSS12200LT1G	NSS40200LT1G	NST3946DXV6T5G
NSR0320MW2T1G	NSS12200WT1G	NSS40200UW6T1G	NST846BF3T5G
NSR0320MW2T3G	NSS12201LT1G	NSS40201LT1G	NST847BF3T5G
NSR0320XV6T1G	NSS12500UW3T2G	NSS40300DDR2G	NST848BF3T5G
NSR0320XV6T5G	NSS12501UW3T2G	NSS40300MDR2G	NST856BF3T5G
NSR0340HT1G	NSS12601CF8T1G	NSS40300MZ4T1G	NST857BF3T5G
NSR0340P2T5G	NSS1C200LT1G	NSS40301MDR2G	NSTB1005DXV5T1G
NSR0340V2T1G	NSS1C200MZ4T1G	NSS40301MZ4T1G	NSTR4501NT1G
NSR0520V2T1G	NSS1C200MZ4T3G	NSS40302PDR2G	NSV1C300ET4G
NSR05F20NXT5G	NSS1C201LT1G	NSS40500UW3T2G	NSV1C301ET4G
NSR05F30NXT5G	NSS1C201MZ4T1G	NSS40501UW3T2G	NSV20200LT1G
NSR05F40NXT5G	NSS1C201MZ4T3G	NSS40600CF8T1G	NSV20201LT1G
NSR0620P2T5G	NSS1C300ET4G	NSS40601CF8T1G	NSV40200LT1G
NSR1020MW2T1G	NSS1C301ET4G	NSS60200LT1G	NSV40201LT1G
NSR1020MW2T3G	NSS20200LT1G	NSS60201LT1G	NSV40300MDR2G
NSR10F20NXT5G	NSS20201LT1G	NSS60600MZ4T1G	NSV40300MZ4T1G
NSR10F30NXT5G	NSS20300MR6T1G	NSS60601MZ4T1G	NSV40301MZ4T1G
NSR10F40NXT5G	NSS20500UW3T2G	NST30010MXV6T1 G	NSV60600MZ4T1G
NSR20F20NXT5G	NSS20501UW3T2G	NST3904DXV6T1G	NSV60600MZ4T3G
NSR20F30NXT5G	NSS20601CF8T1G	NST3904DXV6T5G	NSV60601MZ4T1G
NSR30CM3T5G	NSS30100LT1G	NST3904DXV6T5G	NSV60601MZ4T3G
NSRLV20MW2T1G	NSS30101LT1G	NST3904F3T5G	NSV9435T1G
NSS12100M3T5G	NSS30201MR6T1G	NST3906DXV6T1G	NSVB123JPDV6T1 G
NSS12100UW3TCG	NSS35200CF8T1G	NST3906F3T5G	
NSS12100XV6T1G	NSS35200MR6T1G	NST3946DXV6T1G	NSVB143ZPDV6T1 G

Multisim 14.0 Full Components

NSVB144EPDXV6T1 G	NSVT30010MXV6T1 G	NTB75N06T4G	NTD40N03RT4G
NSVBA114YDXV6T1 G	NSVT3904DXV6T1G	NTBV5605T4G	NTD4302T4G
NSVBAT54WT1G	NTA4001NT1G	NTD110N02RT4G	NTD4804NT4G
NSVBAV70TT1G	NTA4151PT1G	NTD12N10-1G	NTD4805N-1G
NSVBAV70TT3G	NTA4153NT1G	NTD12N10T4G	NTD4805NT4G
NSVBC124EDXV6T1 G	NTA7002NT1G	NTD14N03RT4G	NTD4806N-35G
NSVBCP69T1G	NTB25P06T4G	NTD18N06LT4G	NTD4806NT4G
NSVMMBD353LT1G	NTB30N06LT4G	NTD18N06T4G	NTD4808N-1G
NSVMMBT589LT1G	NTB30N20T4G	NTD20N03L27T4G	NTD4808NT4G
NSVMMBTH10LT1G	NTB45N06LT4G	NTD20N06T4G	NTD4809N-35G
NSVMMUN2132LT1 G	NTB45N06T4G	NTD20P06LG	NTD4809NH-1G
NSVMMUN2232LT1 G	NTB5404NT4G	NTD20P06LT4G	NTD4809NH-35G
NSVMUN2212T1G	NTB5405NT4G	NTD24N06LT4G	NTD4809NHT4G
NSVMUN2233T1G	NTB5605PT4G	NTD24N06T4G	NTD4809NT4G
NSVMUN5131T1G	NTB60N06T4G	NTD2955-1G	NTD4810N-35G
NSVMUN5132T1G	NTB6410ANG	NTD2955G	NTD4810NT4G
NSVMUN5212DW1 T1G	NTB6410ANT4G	NTD2955T4G	NTD4813N-35G
NSVMUN5333DW1 T1G	NTB6411ANG	NTD3055-094-1G	NTD4813NH-1G
NSVMUN5334DW1 T1G	NTB6411ANT4G	NTD3055-094T4G	NTD4813NH-35G
	NTB6412ANG	NTD3055-150T4G	NTD4813NHT4G
	NTB6412ANT4G	NTD3055L104-1G	NTD4813NT4G
	NTB6413ANG	NTD3055L104G	NTD4815N-35G
	NTB6413ANT4G	NTD3055L104T4G	NTD4815NT4G
	NTB75N03L09T4G	NTD3055L170T4G	NTD4855NT4G
		NTD32N06LT4G	NTD4856NT4G

Multisim 14.0 Full Components

NTD4857NT4G	NTD4913N-1G	NTD5807NT4G	NTF5P03T3G
NTD4858N-35G	NTD4913N-35G	NTD5865NL-1G	NTF6P02T3G
NTD4858NT4G	NTD4913NT4G	NTD5865NLT4G	NTGD1100LT1G
NTD4860N-35G	NTD4960N-1G	NTD5867NL-1G	NTGD3149CT1G
NTD4860NT4G	NTD4960N-35G	NTD5867NLT4G	NTGD4161PT1G
NTD4863N-35G	NTD4960NT4G	NTD6414AN-1G	NTGD4167CT1G
NTD4863NAT4G	NTD4963N-1G	NTD6414ANT4G	NTGS3130NT1G
NTD4863NT4G	NTD4963N-35G	NTD6415AN-1G	NTGS3136PT1G
NTD4863NT4H	NTD4963NT4G	NTD6415ANLT4G	NTGS3441PT1G
NTD4865NT4G	NTD4965N-1G	NTD6415ANT4G	NTGS3441T1G
NTD4904N-1G	NTD4965N-35G	NTD6416AN-1G	NTGS3443T1G
NTD4904N-35G	NTD4965NT4G	NTD6416ANL-1G	NTGS3446T1G
NTD4904NT4G	NTD4969N-1G	NTD6416ANLT4G	NTGS4111PT1G
NTD4905N-1G	NTD4969N-35G	NTD6416ANT4G	NTGS4141NT1G
NTD4905N-35G	NTD4969NT4G	NTD6600NT4G	NTGS5120PT1G
NTD4905NT4G	NTD4970N-1G	NTD70N03R-1G	NTHC5513T1G
NTD4906N-1G	NTD4970N-35G	NTD70N03RT4G	NTHD2102PT1G
NTD4906N-35G	NTD4970NT4G	NTDV20N06T4G	NTHD3100CT1G
NTD4906NT4G	NTD5406NT4G	NTE4151PT1G	NTHD3101FT1G
NTD4909N-1G	NTD5407NT4G	NTE4153NT1G	NTHD3102CT1G
NTD4909N-35G	NTD5802NT4G	NTF2955T1G	NTHD3133PFT1G
NTD4909NT4G	NTD5803NT4G	NTF3055-100T1G	NTHD4102PT1G
NTD4910N-1G	NTD5804NT4G	NTF3055-100T3G	NTHD4502NT1G
NTD4910N-35G	NTD5805NT4G	NTF3055L108T1G	NTHD4508NT1G
NTD4910NT4G	NTD5806NT4G	NTF3055L175T1G	NTHD4P02FT1G

Multisim 14.0 Full Components

NTHS4101PT1G	NTK3142PT1G	NTMD4840NR2G	NTMFS4837NHT1G
NTHS4166NT1G	NTLGD3502NT2G	NTMD4884NFR2G	NTMFS4839NHT1G
NTHS5404T1G	NTLGF3402PT2G	NTMD4N03R2G	NTMFS4841NHT1G
NTHS5441T1G	NTLJD3115PT1G	NTMD5836NLR2G	NTMFS4841NT1G
NTHS5443T1G	NTLJD3119CTAG	NTMD5838NLR2G	NTMFS4845NT1G
NTJD1155LT1G	NTLJD3119CTBG	NTMD6N02R2G	NTMFS4846NT1G
NTJD4001NT1G	NTLJD4116NT1G	NTMD6N04R2G	NTMFS4847NAT1G
NTJD4105CT1G	NTLJF3117PT1G	NTMD6P02R2G	NTMFS4847NAT3G
NTJD4105CT2G	NTLJF4156NT1G	NTMFD4901NFT1G	NTMFS4847NT1G
NTJD4152PT1G	NTLJF4156NTAG	NTMFD4901NFT3G	NTMFS4851NT1G
NTJD4158CT1G	NTLJS2103PTBG	NTMFD4902NFT1G	NTMFS4852NT1G
NTJD4158CT2G	NTLJS3113PT1G	NTMFD4902NFT3G	NTMFS4852NT3G
NTJD4401NT1G	NTLJS3113PTAG	NTMFS4108NT1G	NTMFS4897NFT1G
NTJD5121NT1G	NTLJS4114NT1G	NTMFS4119NT1G	NTMFS4897NFT3G
NTJD5121NT2G	NTLLD4901NFTWG	NTMFS4744NT1G	NTMFS4898NFT1G
NTJS3151PT1G	NTLUD3A260PZTAG	NTMFS4821NT1G	NTMFS4898NFT3G
NTJS3157NT1G	NTLUD3A260PZTBG	NTMFS4823NT1G	NTMFS4899NFT1G
NTJS4151PT1G	NTLUF4189NZTAG	NTMFS4823NT3G	NTMFS4899NFT3G
NTJS4160NT1G	NTLUS3A40PZTAG	NTMFS4825NFET1G	NTMFS4921NT1G
NTJS4405NT1G	NTLUS3A40PZTBG	NTMFS4825NFET3G	NTMFS4921NT3G
NTK3043NT1G	NTLUS3A90PZTAG	NTMFS4833NT1G	NTMFS4922NET1G
NTK3134NT1G	NTLUS3A90PZTBG	NTMFS4833NT3G	NTMFS4922NET3G
NTK3134NT5G	NTMD3P03R2G	NTMFS4834NT1G	NTMFS4923NET1G
NTK3139PT1G	NTMD4184PFR2G	NTMFS4835NT1G	NTMFS4923NET3G
NTK3139PT5G	NTMD4820NR2G	NTMFS4836NT1G	NTMFS4925NET1G

Multisim 14.0 Full Components

NTMFS4925NET3G	NTMFS4945NT1G	NTMS5835NLR2G	NTS4173PT1G
NTMFS4925NT1G	NTMFS4983NFT1G	NTMS5838NLR2G	NTS4409NT1G
NTMFS4925NT3G	NTMFS4983NFT3G	NTMS5P02R2G	NTSB20100CT-1G
NTMFS4926NET1G	NTMFS4985NFT1G	NTNS3A65PZT5G	NTSB20U100CT-1G
NTMFS4926NET3G	NTMFS4985NFT3G	NTNUS3171PZT5G	NTSB30100CT-1G
NTMFS4926NT1G	NTMFS5830NLT1G	NTP2955G	NTSB30100S-1G
NTMFS4926NT3G	NTMFS5832NLT1G	NTP35N15G	NTSB30U100CT-1G
NTMFS4927NT1G	NTMS10P02R2G	NTR0202PLT1G	NTSJ20100CTG
NTMFS4927NT3G	NTMS4176PR2G	NTR1P02LT1G	NTSJ2080CTG
NTMFS4931NT1G	NTMS4177PR2G	NTR1P02LT3G	NTSJ20U100CTG
NTMFS4931NT3G	NTMS4503NR2G	NTR2101PT1G	NTSJ30100CTG
NTMFS4934NT1G	NTMS4800NR2G	NTR3161NT1G	NTSJ3080CTG
NTMFS4934NT3G	NTMS4801NR2G	NTR3162PT1G	NTSJ30U80CTG
NTMFS4935NT1G	NTMS4802NR2G	NTR4003NT1G	NTST20100CTG
NTMFS4935NT3G	NTMS4807NR2G	NTR4003NT3G	NTST20120CTG
NTMFS4936NT1G	NTMS4816NR2G	NTR4101PT1G	NTST20U100CTG
NTMFS4936NT3G	NTMS4840NR2G	NTR4170NT1G	NTST30100CTG
NTMFS4937NT1G	NTMS4872NR2G	NTR4171PT1G	NTST30100CTH
NTMFS4937NT3G	NTMS4873NFR2G	NTR4501NT1G	NTST30100SG
NTMFS4939NT1G	NTMS4916NR2G	NTR4502PT1G	NTST30120CTG
NTMFS4939NT3G	NTMS4917NR2G	NTR4502PT3G	NTST30U100CTG
NTMFS4941NT1G	NTMS4920NR2G	NTR4503NT1G	NTST30U100CTH
NTMFS4941NT3G	NTMS4935NR2G	NTS2101PT1G	NTST40120CTG
NTMFS4943NT1G	NTMS4937NR2G	NTS4001NT1G	NTST40120CTH
NTMFS4943NT3G	NTMS4939NR2G	NTS4101PT1G	NTSV20100CTG

Multisim 14.0 Full Components

NTSV20120CTG	NTTFS4985NFTWG	NTZD3155CT2G	NVD5117PLT4G
NTSV20U100CTG	NTTFS4C05NTAG	NTZD3155CT5G	NVD5802NT4G
NTSV30100CTG	NTTFS4C05NTWG	NTZD5110NT1G	NVD5807NT4G
NTSV30120CTG	NTTFS4C06NTAG	NTZS3151PT1G	NVD5865NLT4G
NTTD4401FR2G	NTTFS4C06NTWG	NUMERIC_KEYPAD_ 4X4	NVD5890NT4G
NTTFS4800NTAG	NTTFS4C08NTAG	NUMERIC_KEYPAD_ 4X5	NVD6415ANLT4G
NTTFS4821NTAG	NTTFS4C08NTWG		NVD6824NLT4G
NTTFS4821NTWG	NTTFS4C10NTAG	NUP1105LT1G	NVDD5894NLT4G
NTTFS4823NTAG	NTTFS4C10NTWG	NUP1301	NVF2955T1G
NTTFS4823NTWG	NTTFS4C13NTAG	NUP1301ML3T1G	NVF3055-100T1G
NTTFS4824NTAG	NTTFS4C13NTWG	NUP1301U	NVF3055L108T1G
NTTFS4840NTAG	NTTFS5811NLTAG	NUP2105LT1G	NVF3055L108T3G
NTTFS4929NTAG	NTTFS5811NLTWG	NUP2202W1T2G	NVF5P03T3G
NTTFS4929NTWG	NTTFS5820NLTAG	NUP4102XV6T1G	NVF6P02T3G
NTTFS4932NTAG	NTTFS5820NLTWG	NUP4103FCT1G	NVMD3P03R2G
NTTFS4932NTWG	NTUD3127CT5G	NUP4201DR2G	NVMFD5485NLT1G
NTTFS4937NTAG	NTUD3128NT5G	NUP4201MR6T1G	NVMFD5485NLT3G
NTTFS4937NTWG	NTUD3169CZT5G	NUP4202W1T2G	NVMFD5485NLWFT 1G
NTTFS4939NTAG	NTUD3170NZT5G	NUP4301MR6T1G	NVMFD5485NLWFT 3G
NTTFS4939NTWG	NTUD3171PZT5G	NUP4302MR6T1G	
NTTFS4941NTAG	NTZD3152PT1G	NUP4304MR6T1G	NVMFD5489NLT1G
NTTFS4941NTWG	NTZD3154NT1G	NUP45V6P5T5G	NVMFD5489NLT3G
NTTFS4943NTAG	NTZD3154NT2G	NUS3116MTR2G	NVMFD5489NLWFT 1G
NTTFS4945NTAG	NTZD3154NT5G	NVB6413ANT4G	
NTTFS4985NFTAG	NTZD3155CT1G	NVD4804NT4G	

Multisim 14.0 Full Components

NVMFD5489NLWFT 3G	NVTFS4824NTAG	NX3008PBKV	NZH3V3A
NVMFD5852NLT1G	NVTFS4824NTWG	NX3008PBKW	NZH3V6B
NVMFD5852NLWFT 1G	NVTFS4C25NTAG	NX7002AK	NZH3V9B
NVMFD5873NLT1G	NVTFS5116PLTAG	NX7002AKS	NZH4V3B
NVMFD5873NLWFT 1G	NVTFS5116PLTWG	NX7002AKW	NZH4V7B
NVMFD5877NLT1G	NVTFS5124PLTAG	NXP3875G	NZH5V1B
NVMFD5877NLT3G	NVTFS5124PLTWG	NXP3875Y	NZH5V6B
NVMFD5877NLWFT 1G	NVTFS5826NLTAG	NZ9F2V4ST5G	NZH6V2B
NVMFD5877NLWFT 3G	NVTFS5826NLTWG	NZ9F2V4T5G	NZH6V8B
NVMFS5826NLT1G	NVTJD4001NT1G	NZ9F2V7ST5G	NZH7V5C
NVMFS5826NLT3G	NVTR01P02LT1G	NZ9F5V1T5G	NZH8V2B
NVMFS5832NLT1G	NVTR0202PLT1G	NZ9F6V2ST5G	NZH9V1B
NVMFS5834NLT1G	NVTR4502PT1G	NZH10C	NZL5V6ATT1G
NVMFS5834NLT3G	NVTR4503NT1G	NZH11C	NZL5V6AXV3T1G
NVMFS5844NLT1G	NX2301P	NZH12B	NZL6V8AXV3T1G
NVMFS5844NLT3G	NX3008NBK	NZH13B	NZL7V5AXV3T1G
NVMFS5885NLT1G	NX3008NBKMB	NZH15B	NZQA5V6XV5T1G
NVMFS5885NLT3G	NX3008NBKS	NZH16C	NZQA6V8AXV5T1G
NVMS4816NR2G	NX3008NBKT	NZH18C	NZQA6V8AXV5T2G
NVR5198NLT1G	NX3008NBKV	NZH20C	NZQA6V8AXV5T3G
NVR5198NLT3G	NX3008NBKW	NZH22C	NZX10A
NVTA7002NT1G	NX3008PBK	NZH24C	NZX10C
	NX3008PBKMB	NZH27C	NZX11A
	NX3008PBKS	NZH30C	NZX11C
	NX3008PBKT	NZH3V0B	NZX11D

Multisim 14.0 Full Components

NZX12A	NZX2V4A	NZX6V2D	OP05AH
NZX12B	NZX2V7B	NZX6V2E	OP05AJ
NZX12C	NZX30A	NZX6V8A	OP05AJ8
NZX12D	NZX30C	NZX6V8B	OP05AZ
NZX13B	NZX33C	NZX6V8C	OP05CH
NZX13C	NZX36C	NZX7V5A	OP05CJ
NZX14A	NZX3V0B	NZX7V5B	OP05CJ8
NZX14B	NZX3V3B	NZX7V5D	OP05CN8
NZX14C	NZX3V3C	NZX8V2A	OP05CP
NZX15B	NZX3V6C	NZX8V2B	OP05CZ
NZX16A	NZX3V9C	NZX8V2D	OP05EH
NZX16B	NZX4V3C	NZX9V1B	OP05EJ
NZX16C	NZX4V7A	NZX9V1E	OP05EJ8
NZX18A	NZX4V7C	OCTAL_REG	OP05EN8
NZX18B	NZX4V7D	OL	OP05EP
NZX18C	NZX5V1B	OP01CZ	OP05EZ
NZX20A	NZX5V1C	OP01J	OP05H
NZX20B	NZX5V1D	OP02AJ	OP05J
NZX22A	NZX5V6A	OP02AZ	OP05J8
NZX22B	NZX5V6B	OP02CJ	OP06AJ
NZX24A	NZX5V6C	OP02CP	OP06GJ
NZX24B	NZX5V6D	OP02CZ	OP06GZ
NZX27A	NZX5V6E	OP04AK	OP07AH
NZX27B	NZX6V2B	OP04AY	OP07AJ
NZX27C	NZX6V2C	OP04EY	OP07AJ8

Multisim 14.0 Full Components

OP07AZ	OP09BY	OP15EJ	OP16C
OP07CD	OP10AY	OP15EZ	OP16CH
OP07CH	OP10CY	OP15FH	OP16EH
OP07CJ8	OP10EY	OP15FJ	OP16EJ
OP07CJG	OP10Y	OP15FP	OP16EZ
OP07CN8	OP113EP	OP15FZ	OP16FH
OP07CP	OP113ES	OP15GH	OP16FJ
OP07CS8	OP113FP	OP15GJ	OP16FP
OP07DD	OP113FS	OP15GN8	OP16FZ
OP07DJG	OP1177AR	OP15GP	OP16GH
OP07DP	OP1177ARM	OP15GS	OP16GJ
OP07ED	OP11GP	OP15GZ	OP16GN8
OP07EH	OP11GS	OP160ARC/883	OP16GP
OP07EJ8	OP12BJ	OP160AZ	OP16GS
OP07EJG	OP12BZ/883	OP160FZ	OP16GZ
OP07EN8	OP12EJ	OP160GP	OP176GP
OP07EP	OP12EZ	OP160GS	OP176GS
OP07H	OP15AH	OP162DRU	OP177AZ
OP07J	OP15AJ	OP162GS	OP177BRC/883
OP07J8	OP15AZ	OP162GSZ	OP177BZ
OP07RC/883	OP15BH	OP16AH	OP177EZ
OP07Y	OP15BJ/883	OP16AJ	OP177FP
OP07Z	OP15BZ/883	OP16BH	OP177FS
OP08	OP15CH	OP16BJ/883	OP177FZ
OP09AY	OP15EH	OP16BZ/883	OP177GP

Multisim 14.0 Full Components

OP177GS	OP20GJ	OP215EJ	OP21GP
OP177GZ	OP20GP	OP215EJ8	OP21HS
OP183GP	OP20GZ	OP215EN8	OP220AJ
OP183GS	OP20HJ	OP215EP	OP220AZ
OP184ES	OP20HS	OP215EZ	OP220CJ
OP191GP	OP20HZ	OP215FJ	OP220CZ
OP191GS	OP213AZ/883	OP215FP	OP220EZ
OP193EP	OP213BZ/883	OP215FZ	OP220FZ
OP193ES	OP213EP	OP215GH	OP220GJ
OP193FP	OP213ES	OP215GJ8	OP220GP
OP193FS	OP213EZ	OP215GN8	OP220GS
OP196GP	OP213FP	OP215GP	OP220GZ
OP196GS	OP213FS	OP215GS	OP221AJ/883
OP200AZ	OP215AH	OP215GZ	OP221AZ
OP200EZ	OP215AJ	OP2177AR	OP221BJ
OP200FZ	OP215AJ8	OP2177ARM	OP221CJ
OP200GP	OP215AZ	OP2177ARMZ	OP221EZ
OP200GS	OP215BJ/883	OP2177ARZ	OP221GJ
OP207AY	OP215BRC/883	OP21AJ	OP221GP
OP207EY	OP215BZ/883	OP21AZ	OP221GS
OP207FY	OP215CH	OP21EZ	OP221GZ
OP20BJ	OP215CJ/883	OP21FJ	OP227AJ
OP20BZ	OP215CJ8	OP21FP	OP227CJ
OP20CZ	OP215CZ/883	OP21FZ	OP227EJ
OP20FP	OP215EH	OP21GJ	OP227EN

Multisim 14.0 Full Components

OP227GJ	OP262DRU	OP27CJ8	OP282AZ/883
OP227GN	OP262DRUZ-REEL	OP27CJG	OP282GP
OP22AJ/883	OP262GS	OP27CZ	OP282GS
OP22AZ	OP262GSZ	OP27EH	OP283GP
OP22HP	OP262HRUZ-REEL	OP27EJ	OP283GS
OP22HS	OP270EZ	OP27EJ8	OP284EP
OP22HZ	OP270FZ	OP27EN8	OP284ES
OP237AJ	OP270GP	OP27EP	OP284FP
OP237CJ	OP270GS	OP27EPZ	OP284FS
OP237EJ	OP275GP	OP27EZ	OP285GP
OP237EN	OP275GS	OP27FJ	OP285GS
OP237GJ	OP279GP	OP27FP	OP290ARC/883
OP237GN	OP279GS	OP27FZ	OP290AZ
OP249AJ	OP279HRU	OP27GH	OP290EZ
OP249ARC/883	OP27AH	OP27GJ	OP290FZ
OP249AZ	OP27AJ	OP27GJ8	OP290GP
OP249EJ	OP27AJ8	OP27GJZ	OP290GS
OP249FJ	OP27AJG	OP27GN8	OP291GP
OP249FZ	OP27AL	OP27GP	OP291GS
OP249GP	OP27AZ	OP27GPZ	OP292GP
OP249GS	OP27BJ	OP27GS	OP292GS
OP260AJ	OP27BR/883	OP27GSZ	OP293EP
OP260ARC/883	OP27BZ	OP27GZ	OP293ES
OP260GP	OP27CH	OP281GRU	OP293FP
OP260GS	OP27CJ	OP281GS	OP293FS

Multisim 14.0 Full Components

OP295A	OP37AJ8	OP37GP	OP41GS
OP295AP	OP37AJG	OP37GS	OP420BY
OP295GP	OP37AL	OP37GZ	OP420CRC/883
OP295GS	OP37AZ	OP400ATC/883	OP420CY
OP296GP	OP37BJ	OP400AY	OP420FY
OP296GS	OP37BRC/883	OP400EY	OP420GP
OP296HRU	OP37BZ	OP400FY	OP420GS
OP297ARC/883	OP37CH	OP400GP	OP420GY
OP297AZ	OP37CJ	OP400GS	OP420HP
OP297AZ/883	OP37CJ8	OP400HP	OP420HS
OP297EZ	OP37CJG	OP400HS	OP420HY
OP297FP	OP37CZ	OP413EP	OP421BY
OP297FZ	OP37EH	OP413ES	OP421CY
OP297GP	OP37EJ	OP413EY	OP421FY
OP297GS	OP37EJ8	OP413FP	OP421GP
OP32AZ	OP37EN8	OP413FS	OP421GS
OP32EP	OP37EP	OP4177AR	OP421GY
OP32EZ	OP37EZ	OP4177ARU	OP421HP
OP32FP	OP37FJ	OP4177ARUZ	OP421HS
OP32FZ	OP37FP	OP4177ARZ	OP421HY
OP32GP	OP37FZ	OP41AJ	OP42AJ
OP32GZ	OP37GH	OP41BJ	OP42ARC/883
OP37AFK	OP37GJ	OP41EJ	OP42AZ
OP37AH	OP37GJ8	OP41FJ	OP42EJ
OP37AJ	OP37GN8	OP41GP	OP42EZ

Multisim 14.0 Full Components

OP42FJ	OP470EY	OP493ES	OP61FZ
OP42FZ	OP470GP	OP493FP	OP61GP
OP42GP	OP470GS	OP493FS	OP61GS
OP42GS	OP481GRU	OP495GP	OP64AJ
OP43	OP481GS	OP495GS	OP64ARC/883
OP43A	OP482ARC/883	OP495GSZ	OP64AZ
OP43B	OP482AY/883	OP496GP	OP64GP
OP43E	OP482GP	OP496GS	OP64GS
OP43F	OP484EP	OP496HRU	OP727AR
OP43G	OP484ES	OP497AY	OP727ARU
OP44AJ	OP484FP	OP497BRC/883	OP727ARUZ
OP462DRU	OP484FPZ	OP497BY	OP747AR
OP462DRUZ-REEL	OP484FS	OP497CY	OP747ARU
OP462DS	OP490ATC/883	OP497FP	OP777AR
OP462GS	OP490AY	OP497FS	OP777ARM
OP462GSZ	OP490EY	OP497FY	OP77BJ
OP462HRU-REEL	OP490FY	OP497GP	OP77BRC/883
OP462HRUZ-REEL	OP490GP	OP497GS	OP77BZ
OP467ARC/883	OP490GS	OP497GY	OP77EZ
OP467AY/883	OP491GP	OP50AY	OP77FJ
OP467GP	OP491GS	OP50BY	OP77FZ
OP467GS	OP491GSZ	OP50EY	OP77GP
OP470ARC/883	OP492GP	OP50FY	OP77GS
OP470ATC/883	OP492GS	OP61ARC/883	OP80BJ
OP470AY	OP493EP	OP61AZ	OP80EJ

Multisim 14.0 Full Components

OP80FJ	OPA121KP	OPA137UA	OPA2107AM
OP80GP	OPA121KU	OPA140AID	OPA2107AP
OP80GS	OPA124P	OPA140AIDBVR	OPA2107AU
OP906	OPA124PA	OPA140AIDGKR	OPA2107BM
OP90ARC/883	OPA124PB	OPA140AIDR	OPA2107SM
OP90AZ	OPA124U	OPA141AIDGKR	OPA2111AM
OP90EZ	OPA124UA	OPA141AIDR	OPA2111BM
OP90FZ	OPA124UB	OPA1612AID	OPA2111KM
OP90GP	OPA128JM	OPA1632D	OPA2111KP
OP90GS	OPA128KM	OPA1632DGN	OPA2111SM
OP950	OPA128LM	OPA1642AID	OPA211AID
OP97AJ	OPA128SM	OPA1642AIDGKR	OPA211AIDGKR
OP97AZ	OPA129P	OPA1642AIDR	OPA211AIDR
OP97EP	OPA129PB	OPA1644AID	OPA211AIDRGR
OP97FJ	OPA129U	OPA1644AIPW	OPA211ID
OP97FP	OPA129UB	OPA177EZ	OPA211IDGKR
OP97FS	OPA131PA	OPA177FP	OPA211IDR
OP97FZ	OPA131PJ	OPA177FZ	OPA211IDRGR
OP999	OPA131UA	OPA177GP	OPA2131PA
OPA1013CN8	OPA131UJ	OPA177GS	OPA2131PJ
OPA1013DN8	OPA137N	OPA177GZ	OPA2131UA
OPA111AM	OPA137NA	OPA209AID	OPA2131UJ
OPA111BM	OPA137P	OPA209AIDBVR	OPA2134PA
OPA111SM	OPA137PA	OPA209AIDGKR	OPA2134UA
OPA121KM	OPA137U	OPA209AIDR	OPA2140AID

Multisim 14.0 Full Components

OPA2140AIDGKR	OPA2335AID	OPA2363AIRSVR	OPA2541SM
OPA2140AIDR	OPA2335AIDGKR	OPA2363IDGSR	OPA2544T
OPA2141AIDGKR	OPA2335AIDR	OPA2369AIDCNR	OPA2604AP
OPA2141AIDR	OPA2337EA/250	OPA2369AIDGKR	OPA2604AU
OPA2209AID	OPA2337PA	OPA2373AIDGSR	OPA2613ID
OPA2209AIDGKR	OPA2337UA	OPA2373AIDRCR	OPA2613IDTJ
OPA2209AIDR	OPA2338EA/250	OPA2374AID	OPA2614ID
OPA228P	OPA2338UA	OPA2374AIDCNR	OPA2614IDTJ
OPA228U	OPA2344EA/250	OPA2374AIDG4	OPA2652E
OPA2300AIDGSR	OPA2344PA	OPA2376AID	OPA2652U
OPA2301AID	OPA2344UA	OPA2376AIDGKR	OPA2658P
OPA2301AIDGKR	OPA2347EA	OPA2376AIDR	OPA2658PB
OPA2301AIDR	OPA2347UA	OPA2376AIYZDR	OPA2658U
OPA2317ID	OPA2349EA/250	OPA2377AID	OPA2658UB
OPA2317IDGKR	OPA2349UA	OPA2377AIDGKR	OPA2677T
OPA2330AID	OPA2350EA	OPA2377AIDR	OPA2677U
OPA2330AIDGKR	OPA2350PA	OPA2378AIDCNR	OPA2683ID
OPA2330AIDR	OPA2350UA	OPA2379AID	OPA2683IDCNR
OPA2330AIDRBR	OPA2353EA/250	OPA2379AIDCNR	OPA2683IDG4
OPA2330AIDRG4	OPA2353UA	OPA2379AIDG4	OPA2683IDGST
OPA2333AIDGKR	OPA2354AIDDA	OPA2380AIDGKR	OPA2684ID
OPA2333AIDR	OPA2354AIDGKR	OPA2381AIDGKR	OPA2684IDCNR
OPA2333AIDRBR	OPA2355DGSA/250	OPA2381AIDRBT	OPA2690I-14D
OPA2333AIDRG4	OPA2357AIDGSR	OPA2541AM	OPA2690ID
OPA2334AIDGSR	OPA2363AIDGSR	OPA2541BM	OPA2691I-14D

Multisim 14.0 Full Components

OPA2691ID	OPA27CZ	OPA317IDCKR	OPA344NA
OPA2703EA/250	OPA27EJ	OPA320AIDBVR	OPA344PA
OPA2703PA	OPA27EZ	OPA320SAIDBVR	OPA344UA
OPA2703UA	OPA27FJ	OPA333AID	OPA345NA
OPA2704EA/250	OPA27FZ	OPA333AIDBVR	OPA345UA
OPA2704PA	OPA27GJ	OPA333AIDCKR	OPA347NA
OPA2704UA	OPA27GP	OPA333AIDG4	OPA347PA
OPA2725AID	OPA27GU	OPA334AID	OPA347SA
OPA2725AIDGKR	OPA27GZ	OPA3355EA/250	OPA347UA
OPA2725AIDR	OPA2822E/250	OPA3355UA	OPA348AID
OPA2726AIDGST	OPA2822U	OPA335AID	OPA348AIDBV
OPA2727AID	OPA2835ID	OPA335AIDBV	OPA348AIDCKR
OPA2727AIDRBR	OPA2835IDGS	OPA336N/250	OPA349NA
OPA2727AIDRG4	OPA2835IRMCR	OPA336NA/250	OPA349SA
OPA2735AID	OPA2835IRUNR	OPA336NJ/250	OPA349UA
OPA2735AIDGKR	OPA2836ID	OPA336U	OPA350EA
OPA2735AIDR	OPA2836IDGS	OPA336UA	OPA350PA
OPA2743EA/250	OPA2836IRUNR	OPA337EA/250	OPA350UA
OPA2743PA	OPA2846ID	OPA337NA/250	OPA353NA
OPA2743UA	OPA300AID	OPA337PA	OPA353UA
OPA27AJ	OPA300AIDBV	OPA337UA	OPA354AIDBV
OPA27AZ	OPA301AID	OPA338NA/250	OPA354AIDDA
OPA27BJ	OPA301AIDBV	OPA338UA	OPA355NA
OPA27BZ	OPA317ID	OPA343NA	OPA355UA
OPA27CJ	OPA317IDBVR	OPA343UA	OPA357AIDBV

Multisim 14.0 Full Components

OPA3583AM	OPA379AIDBVR	OPA4131NA	OPA4277PA
OPA3583JM	OPA379AIDCKR	OPA4131NJ	OPA4277UA
OPA358AIDCK	OPA379AIDG4	OPA4131PA	OPA4317ID
OPA360AIDCK	OPA37AJ	OPA4131PJ	OPA4317IPW
OPA363ID	OPA37AZ	OPA4131UA	OPA4330AID
OPA363IDBV	OPA37BJ	OPA4134UA	OPA4330AIPW
OPA364ID	OPA37BZ	OPA4137P	OPA4330AIRGYR
OPA364IDBV	OPA37CJ	OPA4137PA	OPA4342EA
OPA365AID	OPA37CZ	OPA4137U	OPA4342PA
OPA365AIDBVR	OPA37EJ	OPA4137UA	OPA4342UA
OPA3690ID	OPA37EZ	OPA4140AID	OPA4347EA
OPA3690IDBQR	OPA37FJ	OPA4140AIPW	OPA4347UA
OPA3690IDG4	OPA37FZ	OPA4141AID	OPA4348AID
OPA369AIDCKR	OPA37GJ	OPA4141AIPW	OPA4348AIP
OPA373AID	OPA37GP	OPA4209AIPW	OPA4354AID
OPA373AIDBV	OPA37GU	OPA4227PA	OPA4354AIPWR
OPA374AID	OPA37GZ	OPA4227UA	OPA4374AID
OPA374AIDBV	OPA380AID	OPA4228PA	OPA4374AIPWR
OPA377AID	OPA380AIDGK	OPA4228UA	OPA4377AIPW
OPA377AIDBVR	OPA381AIDGK	OPA4241PA	OPA4379AIPWR
OPA377AIDCKR	OPA404AG	OPA4241UA	OPA445AP
OPA377AIDR	OPA404BG	OPA4243EA	OPA445BM
OPA378AIDBVR	OPA404KP	OPA4244EA	OPA445SM
OPA378AIDCKR	OPA404KU	OPA4251PA	OPA452TA
OPA379AID	OPA404SG	OPA4251UA	OPA454AIDDA

Multisim 14.0 Full Components

OPA4650P	OPA512BM	OPA600BM	OPA621KU
OPA4650PB	OPA512SM	OPA600CM	OPA621LG
OPA4650U	OPA541AM	OPA600SM	OPA621SG
OPA4658P	OPA541AP	OPA600TM	OPA622AP
OPA4658PB	OPA541BM	OPA602AM	OPA622AU
OPA4658U	OPA541SM	OPA602AP	OPA623AP
OPA4658UB	OPA544F	OPA602AU	OPA623AU
OPA4684ID	OPA544T	OPA602BM	OPA627AM
OPA4684IPWT	OPA547T	OPA602BP	OPA627AP
OPA4703EA/250	OPA548T	OPA602CM	OPA627AU
OPA4703UA	OPA549S	OPA602SM	OPA627BM
OPA4704EA/250	OPA549T	OPA603AP	OPA627BP
OPA4704UA	OPA551FA/500	OPA603AU	OPA627SM
OPA4743EA/250	OPA551FAKTWT	OPA604AP	OPA628AP
OPA4743UA	OPA551PA	OPA604AU	OPA628AU
OPA4820ID	OPA551UA	OPA606KM	OPA633KP
OPA4820IPWR	OPA552FA/500	OPA606KP	OPA637AM
OPA4872ID	OPA552FAKTWT	OPA606LM	OPA637AP
OPA501AM	OPA552PA	OPA620KG	OPA637AU
OPA501BM	OPA552UA	OPA620KP	OPA637BM
OPA501RM	OPA561PWP	OPA620KU	OPA637BP
OPA501SM	OPA564AIDWD	OPA620LG	OPA637SM
OPA502BM	OPA564AIDWP	OPA620SG	OPA640H
OPA502SM	OPA567AIRHGR	OPA621KG	OPA640HSQ
OPA511AM	OPA569AIDWP	OPA621KP	OPA640P

Multisim 14.0 Full Components

OPA640U	OPA646PB	OPA655UB	OPA682N
OPA640UB	OPA646U	OPA656N	OPA682P
OPA641H	OPA646UB	OPA656U	OPA682U
OPA641HSQ	OPA648H	OPA658N	OPA683BV
OPA641P	OPA648P	OPA658P	OPA683ID
OPA641PB	OPA648U	OPA658U	OPA684ID
OPA641U	OPA650N	OPA659IDBVR	OPA684IDBV
OPA641UB	OPA650NB	OPA659IDRBR	OPA686N
OPA642H	OPA650P	OPA671AP	OPA686U
OPA642HSQ	OPA650PB	OPA675JG	OPA687N
OPA642P	OPA650U	OPA675KG	OPA687U
OPA642PB	OPA650UB	OPA675SG	OPA690ID
OPA642U	OPA651N	OPA676JG	OPA690IDBV
OPA642UB	OPA651NB	OPA676KG	OPA694ID
OPA643H	OPA651P	OPA676SG	OPA694IDBVR
OPA643HSQ	OPA651PB	OPA678AG	OPA698ID
OPA643P	OPA651U	OPA678AP	OPA699ID
OPA643PB	OPA651UB	OPA678AU	OPA703NA
OPA643U	OPA653IDBVR	OPA678SG	OPA703PA
OPA643UB	OPA653IDRBR	OPA680N	OPA703UA
OPA644U	OPA654AM	OPA680P	OPA704NA
OPA644UB	OPA655H	OPA680U	OPA704PA
OPA646H	OPA655HSQ	OPA681N	OPA704UA
OPA646HSQ	OPA655P	OPA681P	OPA725AID
OPA646P	OPA655PB	OPA681U	OPA725AIDBV

Multisim 14.0 Full Components

OPA726AID	OPA842IDBV	OSTV7163151	P6SMB24CAT3G
OPA726AIDGK	OPA847ID	OSTV7203101	P6SMB33A-E3/52
OPA727AIDGKR	OPA847IDBV	OSTV7203151	P6SMB33AT3G
OPA727AIDRBT	OPA860ID	OVERLOAD	P6SMB36A-E3/52
OPA728AIDGKT	OPAMP_3T_VIRTU AL	P4KE10CA-E3/54	P6SMB43CAT3G
OPA728AIDRBT		P4KE300A/3	P6SMB6.8AT3G
OPA734AID	OPAMP_5T_VIRTU AL	P4SMA36CA-E3/61	P6SMB62AT3G
OPA734AIDBV	OPAMP_RATED	P6KE100A-E3/54	P6SMB68AT3G
OPA735AID	OPT301M	P6KE10A-E3/54	PAR_GEN_CHK
OPA735AIDBV	OPTOCOUPLER_VIR TUAL	P6KE200AG	PB_DPST
OPA743NA		P6KE200ARLG	PB_DPST
OPA743PA	OR2	P6KE6.8AG	PB_NC
OPA743UA	OR2	P6KE6.8ARLG	PB_NO
OPA77EZ	OR3	P6KE8.2A-E3/54	PBHV8115T
OPA77FP	OR3	P6KE9.1A-E3/54	PBHV8115X
OPA77FZ	OR4	P6SMB11CAT3G	PBHV8115Z
OPA77GP	OR4	P6SMB13AT3G	PBHV8118T
OPA820ID	OR5	P6SMB15AT3G	PBHV8140Z
OPA820IDBVR	OR5	P6SMB18AT3G	PBHV8215Z
OPA820IDG4	OR6	P6SMB20AT3G	PBHV8540T
OPA827AID	OR6	P6SMB22AT3G	PBHV8540X
OPA827AIDGKR	OR7	P6SMB22CAT3G	PBHV8540Z
OPA835IDBVR	OR7	P6SMB24A-E3/52	PBHV9040T
OPA836IDBVR	OR8	P6SMB24AT3G	PBHV9040X
OPA842ID	OR8	P6SMB24CA-E3/52	PBHV9040Z

Multisim 14.0 Full Components

PBHV9050T	PBLS2024D	PBRN113ET	PBSS302NZ
PBHV9050Z	PBLS4001D	PBRN113ZT	PBSS302PD
PBHV9115T	PBLS4001V	PBRN123ET	PBSS302PX
PBHV9115X	PBLS4001Y	PBRN123YT	PBSS302PZ
PBHV9115Z	PBLS4002D	PBRP113ET	PBSS303ND
PBHV9215Z	PBLS4002V	PBRP113ZT	PBSS303NX
PBHV9540Z	PBLS4002Y	PBRP123ET	PBSS303NZ
PBLS1501V	PBLS4003D	PBRP123YT	PBSS303PD
PBLS1501Y	PBLS4003V	PBSS2515E	PBSS303PX
PBLS1502V	PBLS4003Y	PBSS2515M	PBSS303PZ
PBLS1502Y	PBLS4004D	PBSS2515MB	PBSS304ND
PBLS1503V	PBLS4004V	PBSS2515VPN	PBSS304NX
PBLS1503Y	PBLS4004Y	PBSS2515VS	PBSS304NZ
PBLS1504V	PBLS4005D	PBSS2515YPN	PBSS304PD
PBLS1504Y	PBLS4005V	PBSS2540E	PBSS304PX
PBLS2001D	PBLS4005Y	PBSS2540M	PBSS304PZ
PBLS2001S	PBLS6001D	PBSS2540MB	PBSS305ND
PBLS2002D	PBLS6002D	PBSS301ND	PBSS305NX
PBLS2002S	PBLS6003D	PBSS301NX	PBSS305NZ
PBLS2003D	PBLS6004D	PBSS301NZ	PBSS305PD
PBLS2003S	PBLS6005D	PBSS301PD	PBSS305PX
PBLS2004D	PBLS6021D	PBSS301PX	PBSS305PZ
PBLS2021D	PBLS6022D	PBSS301PZ	PBSS306NX
PBLS2022D	PBLS6023D	PBSS302ND	PBSS306NZ
PBLS2023D	PBLS6024D	PBSS302NX	PBSS306PX

Multisim 14.0 Full Components

PBSS306PZ	PBSS4032SN	PBSS4160PAN	PBSS4350SPN
PBSS3515E	PBSS4032SP	PBSS4160PANP	PBSS4350SS
PBSS3515M	PBSS4032SPN	PBSS4160QA	PBSS4350T
PBSS3515MB	PBSS4041NT	PBSS4160T	PBSS4350X
PBSS3515VS	PBSS4041NX	PBSS4160U	PBSS4350Z
PBSS3540E	PBSS4041NZ	PBSS4160V	PBSS4360Z
PBSS3540M	PBSS4041PT	PBSS4220V	PBSS4420D
PBSS3540MB	PBSS4041PX	PBSS4230PAN	PBSS4440D
PBSS4021NT	PBSS4041PZ	PBSS4230PANP	PBSS4480X
PBSS4021NX	PBSS4041SN	PBSS4230QA	PBSS4520X
PBSS4021NZ	PBSS4041SP	PBSS4230T	PBSS4540X
PBSS4021PT	PBSS4041SPN	PBSS4240DPN	PBSS4540Z
PBSS4021PX	PBSS4112PAN	PBSS4240T	PBSS4560PA
PBSS4021PZ	PBSS4112PANP	PBSS4240V	PBSS4580PA
PBSS4021SN	PBSS4120T	PBSS4240X	PBSS4612PA
PBSS4021SP	PBSS4130PAN	PBSS4240Y	PBSS4620PA
PBSS4021SPN	PBSS4130PANP	PBSS4250X	PBSS4630PA
PBSS4032ND	PBSS4130QA	PBSS4260PAN	PBSS5112PAP
PBSS4032NT	PBSS4130T	PBSS4260PANP	PBSS5120T
PBSS4032NX	PBSS4140DPN	PBSS4260QA	PBSS5130PAP
PBSS4032NZ	PBSS4140T	PBSS4320T	PBSS5130QA
PBSS4032PD	PBSS4140U	PBSS4320X	PBSS5130T
PBSS4032PT	PBSS4140V	PBSS4330PA	PBSS5140T
PBSS4032PX	PBSS4160DPN	PBSS4330X	PBSS5140U
PBSS4032PZ	PBSS4160DS	PBSS4350D	PBSS5140V

Multisim 14.0 Full Components

PBSS5160DS	PBSS5350SS	PBSS9110Y	PDTA114EE
PBSS5160PAP	PBSS5350T	PBSS9110Z	PDTA114EM
PBSS5160QA	PBSS5350X	PBSS9410PA	PDTA114EMB
PBSS5160T	PBSS5350Z	PCP1208-TD-H	PDTA114ET
PBSS5160U	PBSS5360Z	PD15-22B/TR8	PDTA114EU
PBSS5160V	PBSS5420D	PD15-22C/TR8	PDTA114TE
PBSS5220T	PBSS5440D	PD70-01B/TR7	PDTA114TM
PBSS5220V	PBSS5480X	PD93-21C/TR8	PDTA114TMB
PBSS5230PAP	PBSS5520X	PD95-21B/TR10	PDTA114TT
PBSS5230QA	PBSS5540X	PDB-C134	PDTA114TU
PBSS5230T	PBSS5540Z	PDB-C134F	PDTA114YE
PBSS5240T	PBSS5560PA	PDB-C139	PDTA114YM
PBSS5240V	PBSS5580PA	PDB-C142D	PDTA114YMB
PBSS5240X	PBSS5612PA	PDB-C152SM	PDTA114YT
PBSS5240Y	PBSS5620PA	PDB-C156	PDTA114YU
PBSS5250T	PBSS5630PA	PDTA113EE	PDTA115EE
PBSS5250X	PBSS8110D	PDTA113EM	PDTA115EM
PBSS5260PAP	PBSS8110T	PDTA113EMB	PDTA115EMB
PBSS5260QA	PBSS8110X	PDTA113ET	PDTA115ET
PBSS5320D	PBSS8110Y	PDTA113EU	PDTA115EU
PBSS5320T	PBSS8110Z	PDTA113ZE	PDTA115TE
PBSS5320X	PBSS8510PA	PDTA113ZM	PDTA115TM
PBSS5330PA	PBSS9110D	PDTA113ZMB	PDTA115TMB
PBSS5330X	PBSS9110T	PDTA113ZT	PDTA115TT
PBSS5350D	PBSS9110X	PDTA113ZU	PDTA115TU

Multisim 14.0 Full Components

PDTA123EE	PDTA124TM	PDTA143ZM	PDTB113ZT
PDTA123EM	PDTA124TMB	PDTA143ZMB	PDTB123ET
PDTA123EMB	PDTA124TT	PDTA143ZT	PDTB123TT
PDTA123ET	PDTA124TU	PDTA143ZU	PDTB123YT
PDTA123EU	PDTA124XE	PDTA144EE	PDTC114EE
PDTA123JE	PDTA124XM	PDTA144EM	PDTC114EM
PDTA123JM	PDTA124XMB	PDTA144EMB	PDTC114EMB
PDTA123JMB	PDTA124XT	PDTA144ET	PDTC114ET
PDTA123JT	PDTA124XU	PDTA144EU	PDTC114EU
PDTA123JU	PDTA143EE	PDTA144TE	PDTC114TE
PDTA123TM	PDTA143EM	PDTA144TM	PDTC114TM
PDTA123TMB	PDTA143EMB	PDTA144TMB	PDTC114TMB
PDTA123TT	PDTA143ET	PDTA144TT	PDTC114TT
PDTA123TU	PDTA143EU	PDTA144TU	PDTC114TU
PDTA123YE	PDTA143TE	PDTA144VE	PDTC114YE
PDTA123YM	PDTA143TM	PDTA144VM	PDTC114YM
PDTA123YMB	PDTA143TMB	PDTA144VMB	PDTC114YMB
PDTA123YT	PDTA143TT	PDTA144VT	PDTC114YT
PDTA123YU	PDTA143TU	PDTA144VU	PDTC114YU
PDTA124EE	PDTA143XE	PDTA144WE	PDTC115EE
PDTA124EM	PDTA143XM	PDTA144WM	PDTC115EM
PDTA124EMB	PDTA143XMB	PDTA144WMB	PDTC115EMB
PDTA124ET	PDTA143XT	PDTA144WT	PDTC115ET
PDTA124EU	PDTA143XU	PDTA144WU	PDTC115EU
PDTA124TE	PDTA143ZE	PDTB113ET	PDTC115TE

Multisim 14.0 Full Components

PDTC115TM	PDTC124EM	PDTC143XM	PDTC144WM
PDTC115TMB	PDTC124EMB	PDTC143XMB	PDTC144WMB
PDTC115TT	PDTC124ET	PDTC143XT	PDTC144WT
PDTC115TU	PDTC124EU	PDTC143XU	PDTC144WU
PDTC123EE	PDTC124TE	PDTC143ZE	PDTD113ET
PDTC123EM	PDTC124TM	PDTC143ZM	PDTD113ZT
PDTC123EMB	PDTC124TMB	PDTC143ZMB	PDTD123ET
PDTC123ET	PDTC124TT	PDTC143ZT	PDTD123TT
PDTC123EU	PDTC124TU	PDTC143ZU	PDTD123YT
PDTC123JE	PDTC124XE	PDTC144EE	PDZ10B
PDTC123JM	PDTC124XM	PDTC144EM	PDZ11B
PDTC123JMB	PDTC124XMB	PDTC144EMB	PDZ12B
PDTC123JT	PDTC124XT	PDTC144ET	PDZ13B
PDTC123JU	PDTC124XU	PDTC144EU	PDZ15B
PDTC123TE	PDTC143EE	PDTC144TE	PDZ16B
PDTC123TM	PDTC143EM	PDTC144TM	PDZ18B
PDTC123TMB	PDTC143EMB	PDTC144TMB	PDZ2.7B
PDTC123TT	PDTC143ET	PDTC144TT	PDZ20B
PDTC123TU	PDTC143EU	PDTC144TU	PDZ22B
PDTC123YE	PDTC143TE	PDTC144VE	PDZ24B
PDTC123YM	PDTC143TM	PDTC144VM	PDZ3.0B
PDTC123YMB	PDTC143TMB	PDTC144VMB	PDZ3.3B
PDTC123YT	PDTC143TT	PDTC144VT	PDZ3.6B
PDTC123YU	PDTC143TU	PDTC144VU	PDZ3.9B
PDTC124EE	PDTC143XE	PDTC144WE	PDZ4.3B

Multisim 14.0 Full Components

PDZ4.7B	PEMD12	PEMH17	PESD12VS5UD
PDZ5.1B	PEMD13	PEMH18	PESD12VU1UT
PDZ5.6B	PEMD14	PEMH19	PESD12VV1BL
PDZ6.2B	PEMD15	PEMH2	PESD15VL1BA
PDZ6.8B	PEMD16	PEMH20	PESD15VL2BT
PDZ7.5B	PEMD17	PEMH24	PESD15VS1UB
PDZ9.1B	PEMD18	PEMH30	PESD15VS1UL
PEMB1	PEMD19	PEMH4	PESD15VS1ULD
PEMB10	PEMD2	PEMH7	PESD15VS2UAT
PEMB11	PEMD20	PEMH9	PESD15VS2UQ
PEMB13	PEMD24	PEMT1	PESD15VS2UT
PEMB14	PEMD3	PEMX1	PESD15VS4UD
PEMB15	PEMD30	PEMZ1	PESD15VS5UD
PEMB16	PEMD4	PEMZ7	PESD15VU1UT
PEMB17	PEMD48	PESD12VL1BA	PESD16VX1UL
PEMB18	PEMD6	PESD12VL2BT	PESD1CAN
PEMB19	PEMD9	PESD12VS1UA	PESD1FLEX
PEMB2	PEMF21	PESD12VS1UB	PESD1LIN
PEMB20	PEMH1	PESD12VS1UJ	PESD24VL1BA
PEMB24	PEMH10	PESD12VS1UL	PESD24VL2BT
PEMB3	PEMH11	PESD12VS1ULD	PESD24VS1UA
PEMB30	PEMH13	PESD12VS2UAT	PESD24VS1UB
PEMB4	PEMH14	PESD12VS2UQ	PESD24VS1UL
PEMB9	PEMH15	PESD12VS2UT	PESD24VS1ULD
PEMD10	PEMH16	PESD12VS4UD	PESD24VS2UAT

Multisim 14.0 Full Components

PESD24VS2UQ	PESD3V3S2UT	PESD5V0L5UY	PESD5V0U1UB
PESD24VS2UT	PESD3V3S4UD	PESD5V0L6UAS	PESD5V0U1UL
PESD24VS4UD	PESD3V3S4UF	PESD5V0L6US	PESD5V0U1UT
PESD24VS5UD	PESD3V3S5UD	PESD5V0L7BAS	PESD5V0U2BT
PESD24VU1UT	PESD3V3U1UT	PESD5V0L7BS	PESD5V0V1BA
PESD2CAN	PESD3V3V4UF	PESD5V0S1BA	PESD5V0V1BB
PESD36VS1UL	PESD3V3V4UG	PESD5V0S1BB	PESD5V0V1BL
PESD36VS2UT	PESD3V3V4UK	PESD5V0S1BL	PESD5V0V1BLD
PESD3V3L1BA	PESD3V3V4UW	PESD5V0S1BLD	PESD5V0V4UF
PESD3V3L1UA	PESD5V0F1BL	PESD5V0S1UA	PESD5V0V4UG
PESD3V3L1UB	PESD5V0F1BLD	PESD5V0S1UB	PESD5V0V4UK
PESD3V3L1UL	PESD5V0F5UF	PESD5V0S1UJ	PESD5V0V4UW
PESD3V3L2BT	PESD5V0F5UV	PESD5V0S1UL	PESD5V0X1BCAL
PESD3V3L2UM	PESD5V0L1BA	PESD5V0S1ULD	PESD5V0X1BCL
PESD3V3L4UF	PESD5V0L1UA	PESD5V0S2BT	PESD5V0X1BL
PESD3V3L4UG	PESD5V0L1UB	PESD5V0S2UAT	PESD5V0X1BQ
PESD3V3L4UW	PESD5V0L1UL	PESD5V0S2UQ	PESD5V0X1BT
PESD3V3L5UF	PESD5V0L1ULD	PESD5V0S4UD	PESD5V0X1UAB
PESD3V3L5UK	PESD5V0L2BT	PESD5V0S4UF	PESD5V0X1UALD
PESD3V3L5UV	PESD5V0L2UM	PESD5V0S5UD	PESD5V0X1UB
PESD3V3L5UY	PESD5V0L4UF	PESD5V0U1BA	PESD5V0X1ULD
PESD3V3S1UB	PESD5V0L4UG	PESD5V0U1BB	PESD5V2S2UT
PESD3V3S1UL	PESD5V0L4UW	PESD5V0U1BL	PESD9V0V4UK
PESD3V3S2UAT	PESD5V0L5UK	PESD5V0U1BLD	PESD9X5.0L
PESD3V3S2UQ	PESD5V0L5UV	PESD5V0U1UA	PESD9X7.0L

Multisim 14.0 Full Components

PG_13	PIC12C508A	PIC18F6620- TQFP(64L)	PLUS_MINUS_ONE_ ORANGE
PG_9_O_E	PIC12C509		
PHILIPS-MIPS-HDR	PIC12C509A	PIC18F6720- TQFP(64L)	PLUS_MINUS_ONE_ YELLOW
PHN110	PIC12CE518	PIC18F8620- TQFP(80L)	PLVA2656A
PhonePlug	PIC12CE519		PLVA650A
PhonePlug2	PIC12CR509A	PIC18F8720- TQFP(80L)	PLVA662A
PHOTO_DIODE_RA TED	PIC16C505	PIECEWISE_LINEAR _CURRENT	PMBD353
	PIC16C54		PMBD354
PHOTO_TRANSISTO R_RATED	PIC16C54A	PIECEWISE_LINEAR _VOLTAGE	PMBD6050
PHOTODIODE	PIC16C54C		PMBD6100
PHOTOTRANSISTOR	PIC16C554	PIMC31	PMBD7000
		PIMN31	
PHP125	PIC16C558	PIMT1	PMBD7100
PHP225	PIC16C56		PMBD914
		PIMZ2	
PHPT60603NY	PIC16C56A		PMBF170
PHPT60603PY	PIC16C58B	PJ-002B-SMT	PMBF4391
		PJ-007	
PHPT61002NYC	PIC16CR54A		PMBF4392
		PJ1-023	
PHPT61002PYC	PIC16CR54C		PMBF4393
		PJ-102A	
PHPT61003NY	PIC16CR56A		PMBF4416
		PLD-JTAG-HDR	
PHPT61003PY	PIC16CR58B		PMBF4416A
		PLL_VIRTUAL	
PHT4NQ10LT	PIC16CR83		PMBF5484
		PLUS_MINUS_ONE	
PHT6N06LT	PIC16CR84		PMBF5485
		PLUS_MINUS_ONE_ BLUE	
PHT6N06T	PIC16F83		PMBF5486
		PLUS_MINUS_ONE_ GREEN	
PHT6NQ10T	PIC16F84		PMBFJ108
PHT8N06LT	PIC16F84A		PMBFJ109
PIC12C508			PMBFJ110

Multisim 14.0 Full Components

PMBFJ111	PMBT3906	PMBZ5228B	PMBZ5253B
PMBFJ112	PMBT3906M	PMBZ5229B	PMBZ5254B
PMBFJ113	PMBT3906MB	PMBZ5230B	PMBZ5255B
PMBFJ174	PMBT3906VS	PMBZ5231B	PMBZ5256B
PMBFJ175	PMBT3906YS	PMBZ5232B	PMBZ5257B
PMBFJ176	PMBT3946VPN	PMBZ5233B	PMDPB28UN
PMBFJ177	PMBT3946YPN	PMBZ5234B	PMDPB30XN
PMBFJ210	PMBT4401	PMBZ5235B	PMDPB38UNE
PMBFJ211	PMBT4403	PMBZ5236B	PMDPB42UN
PMBFJ212	PMBT5550	PMBZ5237B	PMDPB55XP
PMBFJ308	PMBT5551	PMBZ5238B	PMDPB56XN
PMBFJ309	PMBT6428	PMBZ5239B	PMDPB58UPE
PMBFJ310	PMBT6429	PMBZ5240B	PMDPB70EN
PMBS3904	PMBTA06	PMBZ5241B	PMDPB70XP
PMBS3906	PMBTA13	PMBZ5242B	PMDPB70XPE
PMBT2222	PMBTA14	PMBZ5243B	PMDPB85UPE
PMBT2222A	PMBTA42	PMBZ5244B	PMDPB95XNE
PMBT2369	PMBTA42DS	PMBZ5245B	PMDT290UNE
PMBT2907	PMBTA44	PMBZ5246B	PMDT670UPE
PMBT2907A	PMBTA45	PMBZ5247B	PMEG1020EA
PMBT3904	PMBTA56	PMBZ5248B	PMEG1020EH
PMBT3904M	PMBTA64	PMBZ5249B	PMEG1020EJ
PMBT3904MB	PMBTA92	PMBZ5250B	PMEG1020EV
PMBT3904VS	PMBZ5226B	PMBZ5251B	PMEG1030EH
PMBT3904YS	PMBZ5227B	PMBZ5252B	PMEG1030EJ

Multisim 14.0 Full Components

PMEG2005AEA	PMEG2010EJ	PMEG3005AEV	PMEG3020BER
PMEG2005AEL	PMEG2010EPA	PMEG3005CT	PMEG3020CEP
PMEG2005AELD	PMEG2010EPK	PMEG3005EB	PMEG3020CPA
PMEG2005AESF	PMEG2010ER	PMEG3005EH	PMEG3020DEP
PMEG2005AEV	PMEG2010ET	PMEG3005EJ	PMEG3020EH
PMEG2005BELD	PMEG2010EV	PMEG3005EL	PMEG3020EJ
PMEG2005CT	PMEG2015EA	PMEG3005ELD	PMEG3020EP
PMEG2005EB	PMEG2015EH	PMEG3005ESF	PMEG3020EPA
PMEG2005EH	PMEG2015EJ	PMEG3005ET	PMEG3020ER
PMEG2005EJ	PMEG2015EPK	PMEG3010BEA	PMEG3030BEP
PMEG2005EL	PMEG2015EV	PMEG3010BEP	PMEG3030EP
PMEG2005ELD	PMEG2020AEA	PMEG3010BER	PMEG3050BEP
PMEG2005EPK	PMEG2020CPA	PMEG3010BEV	PMEG3050EP
PMEG2005ESF	PMEG2020EH	PMEG3010CEH	PMEG4002AESF
PMEG2005ET	PMEG2020EJ	PMEG3010CEJ	PMEG4002EB
PMEG2010AEB	PMEG2020EPA	PMEG3010EB	PMEG4002EJ
PMEG2010AEH	PMEG2020EPK	PMEG3010EH	PMEG4002EL
PMEG2010AEJ	PMEG3002AEB	PMEG3010EJ	PMEG4002ELD
PMEG2010AET	PMEG3002AEL	PMEG3010EP	PMEG4002ESF
PMEG2010BEA	PMEG3002AELD	PMEG3010ER	PMEG4005AEA
PMEG2010BELD	PMEG3002AESF	PMEG3010ET	PMEG4005AEV
PMEG2010BER	PMEG3002EJ	PMEG3015EH	PMEG4005CT
PMEG2010BEV	PMEG3002TV	PMEG3015EJ	PMEG4005EH
PMEG2010EA	PMEG3005AEA	PMEG3015EV	PMEG4005EJ
PMEG2010EH	PMEG3005AESF	PMEG3020BEP	PMEG4005EPK

Multisim 14.0 Full Components

PMEG4005ET	PMEG4050ETP	PMF290XN	PMLL5229B
PMEG4010BEA	PMEG45A10EPD	PMF3800SN	PMLL5230B
PMEG4010BEV	PMEG45U10EPD	PMF400UN	PMLL5231B
PMEG4010CEH	PMEG6002EB	PMF63UN	PMLL5232B
PMEG4010CEJ	PMEG6002EJ	PMF77XN	PMLL5233B
PMEG4010CPA	PMEG6002TV	PMF780SN	PMLL5234B
PMEG4010EH	PMEG6010AED	PMF87EN	PMLL5235B
PMEG4010EJ	PMEG6010CEH	PMG45UN	PMLL5236B
PMEG4010EP	PMEG6010CEJ	PMG85XP	PMLL5237B
PMEG4010EPK	PMEG6010CPA	PMGD130UN	PMLL5238B
PMEG4010ER	PMEG6010ELR	PMGD175XN	PMLL5239B
PMEG4010ET	PMEG6010EP	PMGD280UN	PMLL5240B
PMEG4010ETP	PMEG6010ER	PMGD290XN	PMLL5241B
PMEG4010ETR	PMEG6010ETR	PMGD370XN	PMLL5242B
PMEG4015EPK	PMEG6020ELR	PMGD400UN	PMLL5243B
PMEG4020EP	PMEG6020EP	PMGD780SN	PMLL5244B
PMEG4020EPA	PMEG6020EPA	PMGD8000LN	PMLL5245B
PMEG4020EPK	PMEG6020ER	PML260SN	PMLL5246B
PMEG4020ER	PMEG6020ETP	PML340SN	PMLL5247B
PMEG4020ETP	PMEG6020ETR	PMLL4148L	PMLL5248B
PMEG4020ETR	PMEG6030EP	PMLL4448	PMLL5249B
PMEG4030EP	PMEG6030ETP	PMLL5225B	PMLL5250B
PMEG4030ER	PMF170XP	PMLL5226B	PMLL5251B
PMEG4030ETP	PMF250XN	PMLL5227B	PMLL5252B
PMEG4050EP	PMF280UN	PMLL5228B	PMLL5253B

Multisim 14.0 Full Components

PMLL5254B	PMN40LN	PMPB16XN	PMST2907A
PMLL5255B	PMN40UPE	PMPB19XP	PMST3904
PMLL5256B	PMN42XPE	PMPB20EN	PMST3906
PMLL5257B	PMN48XP	PMPB20UN	PMST4401
PMLL5258B	PMN50UPE	PMPB20XPE	PMST4403
PMLL5259B	PMN70XPE	PMPB23XNE	PMST5088
PMLL5260B	PMN80XP	PMPB27EP	PMST5089
PMLL5261B	PMP4201G	PMPB29XNE	PMST5550
PMLL5262B	PMP4201V	PMPB29XPE	PMST5551
PMLL5263B	PMP4201Y	PMPB33XN	PMST6428
PMLL5264B	PMP4501G	PMPB33XP	PMST6429
PMLL5265B	PMP4501V	PMPB43XPE	PMSTA05
PMLL5266B	PMP4501Y	PMPB47XP	PMSTA06
PMMT491A	PMP5201G	PMR280UN	PMSTA42
PMMT591A	PMP5201V	PMR290UNE	PMSTA55
PMN20EN	PMP5201Y	PMR290XN	PMSTA56
PMN22XN	PMP5501G	PMR370XN	PMSTA92
PMN25EN	PMP5501V	PMR400UN	PMT200EN
PMN25UN	PMP5501Y	PMR670UPE	PMT21EN
PMN27UP	PMPB10XNE	PMR780SN	PMT29EN
PMN27XPE	PMPB11EN	PMSS3904	PMT760EN
PMN28UN	PMPB12UN	PMSS3906	PMV117EN
PMN34UN	PMPB13XNE	PMST2222	PMV160UP
PMN34UP	PMPB15XN	PMST2222A	PMV16UN
PMN35EN	PMPB15XP	PMST2369	PMV170UN

Multisim 14.0 Full Components

PMV185XN	PMZB290UN	PN3645	PN5128
PMV20XN	PMZB300XN	PN3646	PN5129
PMV213SN	PMZB350UPE	PN3694	PN5133
PMV22EN	PMZB370UNE	PN4121	PN5134
PMV28UN	PMZB380XN	PN4122	PN5135
PMV30UN	PMZB420UN	PN4141	PN5136
PMV30XN	PMZB670UPE	PN4143	PN5137
PMV31XN	PMZB790SN	PN4248	PN5138
PMV32UP	PN2222	PN4249	PN5139
PMV33UPE	PN2222A	PN4250	PN5142
PMV37EN	PN2369	PN4250A	PN5179
PMV40UN	PN2369A	PN4258	PN5910
PMV45EN	PN2484	PN4258A	PN930
PMV48XP	PN2906	PN4274	PNS40010ER
PMV50UPE	PN2906A	PN4275	POLYNOMIAL_VOLT AGE
PMV60EN	PN2907	PN4354	POTENTIOMETER
PMV65UN	PN2907A	PN4355	POTENTIOMETER_R ATED
PMV65XP	PN3565	PN4356	POTENTIOMETER_V IRTUAL
PMV90EN	PN3638	PN4391	PROBE
PMZ1000UN	PN3638A	PN4392	PROBE_BLUE
PMZ250UN	PN3640	PN4393	PROBE_DIG
PMZ270XN	PN3641	PN4416	PROBE_DIG_BLUE
PMZ350XN	PN3642	PN4416A	PROBE_DIG_GREEN
PMZ390UN	PN3643	PN4916	
PMZ760SN	PN3644	PN4917	

Multisim 14.0 Full Components

PROBE_DIG_ORANGE	PSMN015-60PS	PSMN0R9-25YLC	PSMN2R0-60ES
PROBE_DIG_RED	PSMN016-100PS	PSMN1R0-30YLC	PSMN2R0-60PS
PROBE_DIG_YELLOW	PSMN016-100XS	PSMN1R1-25YLC	PSMN2R1-40PL
PROBE_GREEN	PSMN017-60YS	PSMN1R1-30PL	PSMN2R2-25YLC
PROBE_ORANGE	PSMN017-80PS	PSMN1R1-40BS	PSMN2R2-30YLC
PROBE_RED	PSMN018-80YS	PSMN1R2-25YL	PSMN2R2-40PS
PROBE_YELLOW	PSMN020-100YS	PSMN1R2-25YLC	PSMN2R5-30YL
PRTR5V0U1T	PSMN020-30MLC	PSMN1R2-30YLC	PSMN2R5-60PL
PRTR5V0U2X	PSMN022-30PL	PSMN1R3-30YL	PSMN2R6-30YLC
PSMN011-60ML	PSMN025-100D	PSMN1R5-25YL	PSMN2R6-40YS
PSMN011-60MS	PSMN026-80YS	PSMN1R5-30BLE	PSMN2R6-60PS
PSMN011-80YS	PSMN027-100PS	PSMN1R5-30YL	PSMN2R7-30PL
PSMN012-100YS	PSMN027-100XS	PSMN1R5-30YLC	PSMN2R8-25MLC
PSMN012-60YS	PSMN028-100YS	PSMN1R5-40ES	PSMN2R8-40PS
PSMN012-80PS	PSMN030-60YS	PSMN1R5-40PS	PSMN2R8-80BS
PSMN013-100BS	PSMN034-100PS	PSMN1R6-30PL	PSMN2R9-25YLC
PSMN013-100ES	PSMN038-100YL	PSMN1R6-40YLC	PSMN2R9-30MLC
PSMN013-100PS	PSMN039-100YS	PSMN1R7-30YL	PSMN3R0-30MLC
PSMN013-100XS	PSMN040-100MSE	PSMN1R7-60BS	PSMN3R0-30YL
PSMN013-100YSE	PSMN041-80YL	PSMN1R8-30PL	PSMN3R0-60ES
PSMN013-30MLC	PSMN045-80YS	PSMN1R8-40YLC	PSMN3R0-60PS
PSMN013-30YLC	PSMN057-200B	PSMN1R9-40PL	PSMN3R3-40YS
PSMN013-80YS	PSMN059-150Y	PSMN2R0-30PL	PSMN3R3-60PL
PSMN014-40YS	PSMN069-100YS	PSMN2R0-30YL	PSMN3R3-80BS
	PSMN075-100MSE	PSMN2R0-30YLE	PSMN3R3-80ES

Multisim 14.0 Full Components

PSMN3R3-80PS	PSMN4R6-60PS	PSMN7R0-30YLC	PTVS11VP1UTP
PSMN3R4-30BLE	PSMN4R8-100BSE	PSMN7R0-60YS	PTVS11VS1UR
PSMN3R4-30PL	PSMN5R0-100ES	PSMN7R6-100BSE	PTVS11VS1UTR
PSMN3R5-30YL	PSMN5R0-100PS	PSMN7R6-60PS	PTVS12VP1UP
PSMN3R5-80ES	PSMN5R0-100XS	PSMN7R8-120ES	PTVS12VP1UTP
PSMN3R5-80PS	PSMN5R0-30YL	PSMN7R8-120PS	PTVS12VS1UR
PSMN3R8-100BS	PSMN5R0-80PS	PSMN8R0-40PS	PTVS12VS1UTR
PSMN3R9-25MLC	PSMN5R5-60YS	PSMN8R2-80YS	PTVS13VP1UP
PSMN3R9-60PS	PSMN5R6-100PS	PSMN8R3-40YS	PTVS13VP1UTP
PSMN3R9-60XS	PSMN5R6-100XS	PSMN8R5-100ES	PTVS13VS1UR
PSMN4R0-25YLC	PSMN5R8-40YS	PSMN8R5-100PS	PTVS13VS1UTR
PSMN4R0-30YL	PSMN6R0-25YLB	PSMN8R5-100XS	PTVS14VP1UP
PSMN4R0-30YLD	PSMN6R0-30YL	PSMN8R5-60YS	PTVS14VP1UTP
PSMN4R0-40YS	PSMN6R0-30YLB	PSMN8R7-80PS	PTVS14VS1UR
PSMN4R1-30YLC	PSMN6R0-30YLD	PSMN9R0-25MLC	PTVS14VS1UTR
PSMN4R2-60PL	PSMN6R1-30YLD	PSMN9R5-100PS	PTVS15VP1UP
PSMN4R3-100ES	PSMN6R3-120ES	PSMN9R5-100XS	PTVS15VP1UTP
PSMN4R3-100PS	PSMN6R3-120PS	PSMN9R5-30YLC	PTVS15VS1UR
PSMN4R3-30PL	PSMN6R5-25YLC	PSMN9R8-30MLC	PTVS15VS1UTR
PSMN4R3-80ES	PSMN6R5-80PS	PSMNR90-30BL	PTVS16VP1UP
PSMN4R3-80PS	PSMN7R0-100ES	PTVS10VP1UP	PTVS16VP1UTP
PSMN4R4-30MLC	PSMN7R0-100PS	PTVS10VP1UTP	PTVS16VS1UR
PSMN4R4-80PS	PSMN7R0-100XS	PTVS10VS1UR	PTVS16VS1UTR
PSMN4R5-40PS	PSMN7R0-30MLC	PTVS10VS1UTR	PTVS17VP1UP
PSMN4R6-100XS	PSMN7R0-30YL	PTVS11VP1UP	PTVS17VP1UTP

Multisim 14.0 Full Components

PTVS17VS1UR	PTVS28VS1UTR	PTVS45VP1UP	PTVS60VP1UTP
PTVS17VS1UTR	PTVS30VP1UP	PTVS45VP1UTP	PTVS60VS1UR
PTVS18VP1UP	PTVS30VP1UTP	PTVS45VS1UR	PTVS60VS1UTR
PTVS18VP1UTP	PTVS30VS1UR	PTVS45VS1UTR	PTVS64VP1UP
PTVS18VS1UR	PTVS30VS1UTR	PTVS48VP1UP	PTVS64VP1UTP
PTVS18VS1UTR	PTVS33VP1UP	PTVS48VP1UTP	PTVS6V0P1UP
PTVS20VP1UP	PTVS33VP1UTP	PTVS48VS1UR	PTVS6V0P1UTP
PTVS20VP1UTP	PTVS33VS1UR	PTVS48VS1UTR	PTVS6V0S1UR
PTVS20VS1UR	PTVS33VS1UTR	PTVS51VP1UP	PTVS6V0S1UTR
PTVS20VS1UTR	PTVS36VP1UP	PTVS51VP1UTP	PTVS6V5P1UP
PTVS22VP1UP	PTVS36VP1UTP	PTVS51VS1UR	PTVS6V5P1UTP
PTVS22VP1UTP	PTVS36VS1UR	PTVS51VS1UTR	PTVS6V5S1UR
PTVS22VS1UR	PTVS36VS1UTR	PTVS54VP1UP	PTVS6V5S1UTR
PTVS22VS1UTR	PTVS3V3P1UP	PTVS54VP1UTP	PTVS7V0P1UP
PTVS24VP1UP	PTVS3V3P1UTP	PTVS54VS1UR	PTVS7V0P1UTP
PTVS24VP1UTP	PTVS3V3S1UR	PTVS54VS1UTR	PTVS7V0S1UR
PTVS24VS1UR	PTVS3V3S1UTR	PTVS58VP1UP	PTVS7V0S1UTR
PTVS24VS1UTR	PTVS40VP1UP	PTVS58VP1UTP	PTVS7V5P1UP
PTVS26VP1UP	PTVS40VP1UTP	PTVS58VS1UR	PTVS7V5P1UTP
PTVS26VP1UTP	PTVS40VS1UR	PTVS58VS1UTR	PTVS7V5S1UR
PTVS26VS1UR	PTVS40VS1UTR	PTVS5V0P1UP	PTVS7V5S1UTR
PTVS26VS1UTR	PTVS43VP1UP	PTVS5V0P1UTP	PTVS8V0P1UP
PTVS28VP1UP	PTVS43VP1UTP	PTVS5V0S1UR	PTVS8V0P1UTP
PTVS28VP1UTP	PTVS43VS1UR	PTVS5V0S1UTR	PTVS8V0S1UR
PTVS28VS1UR	PTVS43VS1UTR	PTVS60VP1UP	PTVS8V0S1UTR

Multisim 14.0 Full Components

PTVS8V5P1UP	PUMD14	PUMZ2	PZT751T1G
PTVS8V5P1UTP	PUMD15	PUSH_BUTTON_DP ST	PZTA14
PTVS8V5S1UR	PUMD18	PWM	PZTA42
PTVS8V5S1UTR	PUMD19	PXT2222A	PZTA44
PTVS9V0P1UP	PUMD2	PXT2907A	PZTA92
PTVS9V0P1UTP	PUMD20	PXT4401	PZTA92T1G
PTVS9V0S1UR	PUMD24	PXT4403	PZU10B
PTVS9V0S1UTR	PUMD3	PXTA14	PZU10B1
PULLUP_RATED	PUMD30	PXTA42	PZU10B1A
PULSE_CURRENT	PUMD48	PXTA92	PZU10B2
PULSE_VOLTAGE	PUMD6	PZFJ108	PZU10B2A
PUMB1	PUMD9	PZFJ109	PZU10B2L
PUMB11	PUMH1	PZFJ110	PZU10B3
PUMB13	PUMH10	PZT2222A	PZU10B3A
PUMB14	PUMH11	PZT2222AT1G	PZU10BA
PUMB19	PUMH13	PZT2907A	PZU10BL
PUMB2	PUMH2	PZT2907AT1	PZU10DB2
PUMB24	PUMH30	PZT2907AT1G	PZU11B
PUMB3	PUMH4	PZT2907AT3G	PZU11B1
PUMB30	PUMH7	PZT4401	PZU11B1A
PUMB4	PUMH9	PZT4403	PZU11B2
PUMB9	PUMT1	PZT651T1	PZU11B2A
PUMD10	PUMX1	PZT651T1G	PZU11B2L
PUMD12	PUMX2	PZT751T1	PZU11B3
PUMD13	PUMZ1		PZU11B3A

Multisim 14.0 Full Components

PZU11BA	PZU14B2	PZU16DB2	PZU20B1
PZU11BL	PZU14B2A	PZU18B	PZU20B1A
PZU11DB2	PZU14B2L	PZU18B1	PZU20B2
PZU12B	PZU14DB2	PZU18B1A	PZU20B2A
PZU12B1	PZU15B	PZU18B2	PZU20B2L
PZU12B1A	PZU15B1	PZU18B2A	PZU20B3
PZU12B2	PZU15B1A	PZU18B2L	PZU20B3A
PZU12B2A	PZU15B2	PZU18B3	PZU20BA
PZU12B2L	PZU15B2A	PZU18B3A	PZU20BL
PZU12B3	PZU15B2L	PZU18BA	PZU20DB2
PZU12B3A	PZU15B3	PZU18BL	PZU22B
PZU12BA	PZU15B3A	PZU18DB2	PZU22B1
PZU12BL	PZU15BA	PZU2.4B	PZU22B1A
PZU12DB2	PZU15BL	PZU2.4BA	PZU22B2
PZU13B	PZU15DB2	PZU2.4BL	PZU22B2A
PZU13B1	PZU16B	PZU2.7B	PZU22B2L
PZU13B1A	PZU16B1	PZU2.7B1	PZU22B3
PZU13B2	PZU16B1A	PZU2.7B1A	PZU22B3A
PZU13B2A	PZU16B2	PZU2.7B2	PZU22BA
PZU13B2L	PZU16B2A	PZU2.7B2A	PZU22BL
PZU13B3	PZU16B2L	PZU2.7B2L	PZU22DB2
PZU13B3A	PZU16B3	PZU2.7BA	PZU24B
PZU13BA	PZU16B3A	PZU2.7BL	PZU24B1
PZU13BL	PZU16BA	PZU2.7DB2	PZU24B1A
PZU13DB2	PZU16BL	PZU20B	PZU24B2

Multisim 14.0 Full Components

PZU24B2A	PZU3.3BA	PZU33BA	PZU4.7BL
PZU24B2L	PZU3.3BL	PZU33BL	PZU4.7DB2
PZU24B3	PZU3.3DB2	PZU36B	PZU5.1B
PZU24B3A	PZU3.6B	PZU36BA	PZU5.1B1
PZU24BA	PZU3.6B1	PZU36BL	PZU5.1B1A
PZU24BL	PZU3.6B1A	PZU4.3B	PZU5.1B2
PZU24DB2	PZU3.6B2	PZU4.3B1	PZU5.1B2A
PZU27B	PZU3.6B2A	PZU4.3B1A	PZU5.1B2L
PZU27BA	PZU3.6B2L	PZU4.3B2	PZU5.1B3
PZU27BL	PZU3.6BA	PZU4.3B2A	PZU5.1B3A
PZU3.0B	PZU3.6BL	PZU4.3B2L	PZU5.1BA
PZU3.0B1	PZU3.6DB2	PZU4.3B3	PZU5.1BL
PZU3.0B1A	PZU3.9B	PZU4.3B3A	PZU5.1DB2
PZU3.0B2	PZU3.9B1	PZU4.3BA	PZU5.6B
PZU3.0B2A	PZU3.9B1A	PZU4.3BL	PZU5.6B1
PZU3.0B2L	PZU3.9B2	PZU4.3DB2	PZU5.6B1A
PZU3.0BA	PZU3.9B2A	PZU4.7B	PZU5.6B2
PZU3.0BL	PZU3.9B2L	PZU4.7B1	PZU5.6B2A
PZU3.0DB2	PZU3.9BA	PZU4.7B1A	PZU5.6B2L
PZU3.3B	PZU3.9BL	PZU4.7B2	PZU5.6B3
PZU3.3B1	PZU3.9DB2	PZU4.7B2A	PZU5.6B3A
PZU3.3B1A	PZU30B	PZU4.7B2L	PZU5.6BA
PZU3.3B2	PZU30BA	PZU4.7B3	PZU5.6BL
PZU3.3B2A	PZU30BL	PZU4.7B3A	PZU5.6DB2
PZU3.3B2L	PZU33B	PZU4.7BA	PZU6.2B

Multisim 14.0 Full Components

PZU6.2B1	PZU7.5B2A	PZU9.1B3A	RC4136D
PZU6.2B1A	PZU7.5B2L	PZU9.1BA	RC4136N
PZU6.2B2	PZU7.5B3	PZU9.1BL	RC4558D
PZU6.2B2A	PZU7.5B3A	PZU9.1DB2	RC4558P
PZU6.2B2L	PZU7.5BA	QL6250-4PQ208C	RC4558Y
PZU6.2B3	PZU7.5BL	QUAD_MUX_2TO1	RC4559D
PZU6.2B3A	PZU7.5DB2	QUAD_REG	RC4559P
PZU6.2BA	PZU8.2B	R145-32.768kHz	RCJ-011-SMT
PZU6.2BL	PZU8.2B1	R26-32.768kHz	RCJ-32234
PZU6.2DB2	PZU8.2B1A	R38-32.768kHz	RD10
PZU6.8B	PZU8.2B2	R710XPT	RD11
PZU6.8B1	PZU8.2B2A	R711XPT	RD12
PZU6.8B1A	PZU8.2B2L	R712XPT	RD15
PZU6.8B2	PZU8.2B3	R714XPT	RD15SB
PZU6.8B2A	PZU8.2B3A	RB520CS3002L	RD2.0S
PZU6.8B2L	PZU8.2BA	RB520CS30L	RD2.2S
PZU6.8B3	PZU8.2BL	RB520S30	RD2.4S
PZU6.8B3A	PZU8.2DB2	RB521CS30L	RD2.7S
PZU6.8BA	PZU9.1B	RB521S30	RD3.0S
PZU6.8BL	PZU9.1B1	RB521S30T1G	RD4.7
PZU6.8DB2	PZU9.1B1A	RB521S30T5G	RD5.1
PZU7.5B	PZU9.1B2	RB751CS40	RD5.6
PZU7.5B1	PZU9.1B2A	RB751S40	RD6.2
PZU7.5B1A	PZU9.1B2L	RB751S40T1G	RD6.8
PZU7.5B2	PZU9.1B3	RB751V40	RD7.5

Multisim 14.0 Full Components

RD7.5SB	REF191ES	REF196GSZ	REF3325AIDBZR
RD8.2	REF191GP	REF198ES	REF3325AIDCKR
RD9.2	REF191GS	REF198FSZ	REF3330AIDBZR
REF01AJ	REF192ES	REF198GP	REF3330AIDCKR
REF01AJ/883C	REF192FS	REF198GRU	REF3333AIDBZR
REF01CJ	REF192GP	REF198GRUZ	REF3333AIDCKR
REF01CP	REF192GPZ	REF198GS	REF43FZ
REF01CPZ	REF192GRU	REF3012_SOT23_3	REF43GP
REF01CS	REF192GRUZ	REF3020_SOT23_3	REF43GPZ
REF01EZ	REF192GS	REF3025_SOT23_3	REF43GS
REF01HPZ	REF193GS	REF3033_SOT23_3	REF5010AID
REF01HS	REF193GSZ	REF3040_SOT23_3	REF5010AIDGKR
REF01HZ	REF194ES	REF3120AIDBZR	REF5010ID
REF02AJ	REF194GP	REF3212AIDBVR	REF5010IDGKR
REF02AJ/883C	REF194GSZ	REF3220AIDBVR	REF5020AID
REF02AZ	REF195ES	REF3225AIDBVR	REF5020AIDGKR
REF02CP	REF195FS	REF3230AIDBVR	REF5020ID
REF02CS	REF195GP	REF3233AIDBVR	REF5020IDGKR
REF02CZ	REF195GPZ	REF3240AIDBVR	REF5025AID
REF02EZ	REF195GRU	REF3312AIDBZR	REF5025AIDGKR
REF02HPZ	REF195GRUZ	REF3312AIDCKR	REF5025ID
REF02HSZ	REF195GS	REF3318AIDBZR	REF5025IDGKR
REF02HZ	REF196GRU	REF3318AIDCKR	REF5030AID
REF02RC	REF196GRU-REEL7	REF3320AIDBZR	REF5030AIDGKR
REF02RC/883C	REF196GS	REF3320AIDCKR	REF5030ID

Multisim 14.0 Full Components

REF5030IDGKR	RELAY1A_VIRTUAL	RGP02-20E	RGP25G
REF5030IDR	RELAY1B_VIRTUAL	RGP02-20E-E3/54	RGP25J
REF5040AID	RELAY1C_VIRTUAL	RGP10A	RGP25K
REF5040AIDGKR	RESISTOR_RATED	RGP10B	RGP25M
REF5040AIDR	RESISTOR_VIRTUAL	RGP10D	RGP30A
REF5040ID	REVERSE_1A	RGP10G	RGP30B
REF5040IDGKR	REVERSE_2A	RGP10J	RGP30D
REF5040IDR	REVERSE_3A	RGP10K	RGP30G
REF5045AID	REVERSE_4A	RGP10M	RGP30J
REF5045AIDGKR	RGF1A	RGP10M-E3/54	RGP30K
REF5045AIDR	RGF1B	RGP15A	RGP30M
REF5045ID	RGF1D	RGP15B	R-HI-008068-2
REF5045IDGKR	RGF1G	RGP15D	RIBBON_10H
REF5045IDR	RGF1J	RGP15G	RIBBON_10H_LATC H
REF5050AID	RGF1K	RGP15J	RIBBON_10H_MNT
REF5050AIDGKR	RGF1M	RGP15K	RIBBON_10V
REF5050AIDR	RGL34A	RGP15M	RIBBON_10V_LATC H
REF5050ID	RGL34B	RGP20A	RIBBON_10V_MNT
REF5050IDGKR	RGL34D	RGP20B	RIBBON_14H
REF5050IDR	RGL34G	RGP20D	RIBBON_14H_LATC H
REG_FILE_2Px4	RGL34J	RGP20G	RIBBON_14H_MNT
REG_FILE_4x4	RGP02-12E	RGP20J	RIBBON_14V
RELAY_NC	RGP02-14E	RGP25A	
RELAY_NO	RGP02-16E	RGP25B	
RELAY_NONC	RGP02-18E	RGP25D	

Multisim 14.0 Full Components

RIBBON_14V_LATC H	RIBBON_26H_LATC H	RIBBON_40V_LATC H	S1227-1010BQ
			S1227-1010BR
RIBBON_14V_MNT	RIBBON_26H_MNT	RIBBON_40V_MNT	S1227-16BQ
RIBBON_16H	RIBBON_26V	RIBBON_50H	S1227-16BR
RIBBON_16H_LATC H	RIBBON_26V_LATC H	RIBBON_50H_LATC H	S1227-33BQ
RIBBON_16H_MNT	RIBBON_26V_MNT	RIBBON_50H_MNT	S1227-33BR
RIBBON_16V	RIBBON_30H	RIBBON_50V	S1227-66BQ
RIBBON_16V_LATC H	RIBBON_30H_LATC H	RIBBON_50V_LATC H	S1227-66BR
RIBBON_16V_MNT	RIBBON_30H_MNT	RIBBON_50V_MNT	S1B-E3/61T
RIBBON_20H	RIBBON_30V	RM4136FK	S1D-E3/61T
RIBBON_20H_LATC H	RIBBON_30V_LATC H	RM4136J	S1G-E3/61T
RIBBON_20H_MNT	RIBBON_30V_MNT	RM4136W	S1J-E3/61T
RIBBON_20V	RIBBON_34H	RM4558JG	S1PG-E3/84A
RIBBON_20V_LATC H	RIBBON_34H_LATC H	RMB4S-E3/45	S2800A
RIBBON_20V_MNT	RIBBON_34H_MNT	RS1G-E3/5AT	S2800B
RIBBON_24H	RIBBON_34V	RS1K-E3/61T	S2800D
RIBBON_24H_LATC H	RIBBON_34V_LATC H	RS2D-E3/52T	S2800M
RIBBON_24H_MNT	RIBBON_34V_MNT	RS2J-E3/52T	S2G-E3/52T
RIBBON_24V	RIBBON_40H	RS3D-E3/57T	S2SA1774G
RIBBON_24V_LATC H	RIBBON_40H_LATC H	RTD	S2SC4617G
RIBBON_24V_MNT	RIBBON_40H_MNT	RV4136D	S3D-E3/57T
RIBBON_26H	RIBBON_40V	RV4136N	S3M-E3/57T
		RV4558D	S4PD-M3/86A
		RV4558P	S5227B
			S5227G

Multisim 14.0 Full Components

S5227J	SAF-XC866-1FRA AB	SAF-XC888CM-6FFA 5V AC	SAK-XC2285M- 104F80L AA
S5227N	SAF-XC866L-1FRA AB	SAF-XC888LM-6FFA 5V AC	SAK-XC2285M- 104F80L AA
SA15AG	SAF-XC866L-1FRA AB	SAF-XC888LM-6FFA 5V AC	SAK-XC2285M- 56F80L AA
SA15ARLG	SAF-XC886-6FFA 5V AC	SAK-C167CR-LM HA+	SAK-XC2285M- 56F80L AA
SA2M-E3/5AT	SAF-XC886-6FFA 5V AC	SAK-C167CR-LM HA+	SAK-XC2285M- 72F80L AA
SA5.0A-E3/54	SAF-XC886CLM- 6FFA 5V AC	SAK-C167SR-LM HA+	SAK-XC2285M- 72F80L AA
SA5.0CA-E3/54	SAF-XC886CLM- 6FFA 5V AC	SAK-C167SR-LM HA+	SAK-XC2286-56F66L AC
SA6.0A-E3/54	SAF-XC886CM-6FFA 5V AC	SAK-XC2264-56F66L AC	SAK-XC2286-56F66L AC
SA6.0CA-E3/54	SAF-XC886CM-6FFA 5V AC	SAK-XC2264-56F66L AC	SAK-XC2286-56F80L AC
SA9.0CA-E3/54	SAF-XC886LM-6FFA 5V AC	SAK-XC2264-56F80L AC	SAK-XC2286-56F80L AC
SAB-C167CR-LM HA+	SAF-XC886LM-6FFA 5V AC	SAK-XC2264-56F80L AC	SAK-XC2287-56F66L AC
SAB-C167CR-LM HA+	SAF-XC888-6FFA 5V AC	SAK-XC2267-56F66L AC	SAK-XC2287-56F66L AC
SAB-C167SR-LM HA+	SAF-XC888-6FFA 5V AC	SAK-XC2267-56F66L AC	SAK-XC2287-56F80L AC
SAB-C167SR-LM HA+	SAF-XC888CLM- 6FFA 5V AC	SAK-XC2267-56F80L AC	SAK-XC2287-56F80L AC
SAC5.0-E3/54	SAF-XC888CLM- 6FFA 5V AC	SAK-XC2267-56F80L AC	SAK-XC2287-96F66L AC
SAF-C167CR-LM HA+	SAF-XC888CM-6FFA 5V AC		
SAF-C167CR-LM HA+			
SAF-XC164TM- 4F40F AA			
SAF-XC164TM- 4F40F AA			
SAF-XC866-1FRA AB			

Multisim 14.0 Full Components

SAK-XC2287-96F66L AC	SAK-XC866L-1FRA AB	SAK-XC888LM-6FFA 5V AC	SB350
			SB360
SAK-XC2287-96F80L AC	SAK-XC886-6FFA 5V AC	SAK-XC888LM-6FFA 5V AC	SB3H100-E3/54
SAK-XC2287-96F80L AC	SAK-XC886-6FFA 5V AC	SAMPLE_BEND	SB520
		SAMPLE_GENERIC	SB530
SAK-XC2287M- 104F80L AA	SAK-XC886CLM- 6FFA 5V AC	SAMPLE_LOSSY	SB540
SAK-XC2287M- 104F80L AA	SAK-XC886CLM- 6FFA 5V AC	SAMPLE_MICROSTR IP	SB540-E3/54
			SB550
SAK-XC2287M- 56F80L AA	SAK-XC886CM-6FFA 5V AC	SAMPLE_OPENEND	SB560
		SAMPLE_RFCAP	SB560-E3/54
SAK-XC2287M- 56F80L AA	SAK-XC886CM-6FFA 5V AC	SAMPLE_RFCOIL	SBAS16DXV6T1G
SAK-XC2287M- 72F80L AA	SAK-XC886LM-6FFA 5V AC	SAMPLE_WAVEGUI DE	SBAS20LT1G
		SB	SBAT54CLT1G
SAK-XC2287M- 72F80L AA	SAK-XC886LM-6FFA 5V AC	SB01-15C-TB-E	SBAV70LT1G
			SBAV70LT3G
SAK-XC2766X- 96F66L AC	SAK-XC888-6FFA 5V AC	SB040-E3/54	SBAV99LT1G
		SB05-03Q-TL-E	SBAV99LT3G
SAK-XC2766X- 96F66L AC	SAK-XC888-6FFA 5V AC	SB1003M3-TL-E	SBAW56LT1G
		SB140A-E3/54	SBAW56LT3G
SAK-XC2786X- 96F66L AC	SAK-XC888CLM- 6FFA 5V AC	SB160-E3/54	SBAW56TT1G
SAK-XC2786X- 96F66L AC	SAK-XC888CLM- 6FFA 5V AC	SB2H100-E3/54	SBC807-16LT1G
		SB2H90-E3/23	SBC807-16LT3G
SAK-XC866-1FRA AB	SAK-XC888CM-6FFA 5V AC	SB320	SBC807-25LT1G
SAK-XC866-1FRA AB			SBC807-25LT3G
SAK-XC866L-1FRA AB	SAK-XC888CM-6FFA 5V AC	SB330	SBC807-25LT3G
		SB340	SBC807-40LT1G

Multisim 14.0 Full Components

SBC807-40LT3G	SBR660CTT4G	SBRD8835LG	SE5534FK
SBC817-25LT1G	SBR80520LT1G	SBRD8835LT4G	SE5534JG
SBC817-25LT3G	SBR80520LT3G	SBRS81100T3G	SEAM-40-03.0-S-06-2-A-K-TR
SBC846ALT1G	SBR835LT4G	SBRS8120T3G	SEAM-40-07.0-S-06-2-A-K-TR
SBC846BDW1T1G	SBRA8160T3G	SBRS8130LT3G	SEMICONDUCTOR_CAPACITOR_VIRTUAL
SBC846BLT1G	SBRB1045G	SBRS8140T3G	SEMICONDUCTOR_RESISTOR_VIRTUAL
SBC846BLT3G	SBRB1045T4G	SBRS8190T3G	SEVEN_SEG_COM_A
SBC846BPDW1T1G	SBRB1545CTG	SBRS8320T3G	SEVEN_SEG_COM_A_BLUE
SBC846BPDW1T2G	SBRB1545CTT4G	SBRS8340T3G	SEVEN_SEG_COM_A_GREEN
SBC847BDW1T1G	SBRB20200CTT4G	SBS811-TL-E	SEVEN_SEG_COM_A_ORANGE
SBC847BDW1T3G	SBRB2545CTG	SCH2202-TL-E	SEVEN_SEG_COM_A_YELLOW
SBC856ALT1G	SBRB2545CTT4G	SCHMITT_TRIGGER	SEVEN_SEG_COM_K
SBC856BDW1T1G	SBRD81035CTLT4G	SCR	SEVEN_SEG_COM_K_BLUE
SBC856BDW1T3G	SBRD81045T4G	SD05T1G	SEVEN_SEG_COM_K_GREEN
SBC856BWT1G	SBRD8320G	SD12CT1G	SEVEN_SEG_COM_K_ORANGE
SBC857BDW1T1G	SBRD8320T4G	SD12T1G	SEVEN_SEG_COM_K_YELLOW
SBCP56-10T1G	SBRD8330G	SD241	SEVEN_SEG_COM_K_ORANGE
SBCP56-16T1G	SBRD8330T4G	SD41	SEVEN_SEG_COM_K_ORANGE
SBCP56-16T3G	SBRD8340G	SDTA114YET1G	SEVEN_SEG_COM_K_ORANGE
SBCP56T1G	SBRD8340T4G	SDTC114EET1G	SEVEN_SEG_COM_K_ORANGE
SBCP56T3G	SBRD8350G	SDTC114YET1G	SEVEN_SEG_COM_K_ORANGE
SBCP68T1G	SBRD8350T4G	SDTC124EET1G	SEVEN_SEG_COM_K_ORANGE
SBE001-TL-E	SBRD8360G	SE10PJ-M3/84A	SEVEN_SEG_COM_K_ORANGE
SBE002-TL-E	SBRD8360RLG	SE5534AFK	SEVEN_SEG_COM_K_ORANGE
SBR640CTT4G	SBRD8360T4G	SE5534AJG	SEVEN_SEG_COM_K_ORANGE

Multisim 14.0 Full Components

SEVEN_SEG_DECIMAL_COM_A	SEVEN_SEG_TWO-DIGIT_COM_A_ORANGE	SFH6136-X006	SFH6700-X009
SEVEN_SEG_DECIMAL_COM_A_BLUE	SEVEN_SEG_TWO-DIGIT_COM_A_YELLOW	SFH6136-X007	SFH6701
SEVEN_SEG_DECIMAL_COM_A_GREEN	SEVEN_SEG_TWO-DIGIT_COM_K_BLUE	SFH6136-X009T	SFH6701-X007
SEVEN_SEG_DECIMAL_COM_A_ORANGE	SEVEN_SEG_TWO-DIGIT_COM_K_GREEN	SFH6136-X016	SFH6701-X009
SEVEN_SEG_DECIMAL_COM_A_YELLOW	SEVEN_SEG_TWO-DIGIT_COM_K_ORANGE	SFH6136-X017T	SFH6702
SEVEN_SEG_DECIMAL_COM_K	SEVEN_SEG_TWO-DIGIT_COM_K_YELLOW	SFH6136-X018	SFH6702-X006
SEVEN_SEG_DECIMAL_COM_K_BLUE	SFH 203 FA	SFH6136-X019T	SFH6702-X007
SEVEN_SEG_DECIMAL_COM_K_GREEN	SFH 205 F	SFH6156-3	SFH6702-X009T
SEVEN_SEG_DECIMAL_COM_K_ORANGE	SFH 206 K	SFH6156-3T	SFH6705
SEVEN_SEG_DECIMAL_COM_K_YELLOW	SFH 213	SFH615A-3	SFH6705-X006
SEVEN_SEG_TWO-DIGIT_COM_A	SFH 229 FA	SFH615A-3X001	SFH6705-X007
SEVEN_SEG_TWO-DIGIT_COM_A_BLUE	SFH 2400 FA	SFH615A-3X006	SFH6711
SEVEN_SEG_TWO-DIGIT_COM_A_GREEN	SFH 2500 FA-Z	SFH615A-3X007T	SFH6711-X007
SEVEN_SEG_TWO-DIGIT_COM_A_ORANGE	SFH 2505 FA-Z	SFH615A-3X009T	SFH6712
SEVEN_SEG_TWO-DIGIT_COM_A_YELLOW	SFH6136	SFH615A-3X016	SFH6712-X007
SEVEN_SEG_TWO-DIGIT_COM_K_BLUE	SFH6136-X001	SFH615A-3X017	SFH6719
SEVEN_SEG_TWO-DIGIT_COM_K_GREEN		SFH617A-3	SFH6720T
SEVEN_SEG_TWO-DIGIT_COM_K_ORANGE		SFH617A-3X001	SFH6721T
SEVEN_SEG_TWO-DIGIT_COM_K_YELLOW		SFH617A-3X006	SFH6755T
		SFH617A-3X007T	SFH6756T
		SFH617A-3X016	SFH6757T
		SFH617A-3X017T	SFH690CT
		SFH6316T	SFH690C-X001T
		SFH6343T	SFT1341-E
		SFH6700	SFT1341-TL-E

Multisim 14.0 Full Components

SFT1345-H	Si2374DS-T1-GE3	SiA922EDJ-T1-GE3	SL22-E3/52T
SFT1345-TL-H	Si5936DU-T1-GE3	SiA931DJ-T1-GE3	SL23-E3/52T
SFT1423-E	Si7121ADN-T1-GE3	SiA936EDJ-T1-GE3	SL43-E3/57T
SFT1423-TL-E	Si7149ADP-T1-GE3	SiHB23N60E-GE3	SL44-E3/57T
SFT1440-E	Si7456CDP-T1-GE3	SiHB33N60E-GE3	SLOW_1A
SFT1440-H	Si8406DB-T2-E1	SiHF23N60E-GE3	SLOW_2A
SFT1440-TL-E	Si8416DB-T2-E1	SiHG33N60E-GE3	SLOW_3A
SFT1440-TL-H	Si8424CDB-T1-E1	SiHG64N65E-GE3	SLOW_4A
SGL41-40-E3/96	Si8425DB-T1-E1	SiHG73N60E-GE3	SM05T1G
SHIFT_4BIDI	Si8461DB-T2-E1	SiHP33N60E-GE3	SM12T1G
SHIFT_4PIPO	Si8469DB-T2-E1	SiJ470DP-T1-GE3	SM15T150A-E3/57T
SHIFT_8PIN	Si8483DB-T2-E1	SiJ478DP-T1-GE3	SM15T150CA-E3/9AT
SHIFT_8POUT	Si8487DB-T1-E1	SiR472ADP-T1-GE3	SM15T18A-E3/57T
Si1016CX-T1-GE3	Si8497DB-T2-E1	SiR640ADP-T1-GE3	SM15T24A-E3/9AT
Si1050X-T1-GE3	Si8499DB-T2-E1	SiR644DP-T1-GE3	SM15T33A-E3/57T
Si1069X-T1-GE3	Si8800EDB-T2-E1	SiR880ADP-T1-GE3	SM15T68A-E3/57T
Si1070X-T1-GE3	Si8802DB-T2-E1	SiS435DNT-T1-GE3	SM15T68CA-E3/57T
Si1071X-T1-GE3	Si8851EDB-T2-E1	SiS439DNT-T1-GE3	SM3G45
Si1317DL-T1-GE3	SiA413ADJ-T1-GE3	SiS443DN-T1-GE3	SM3J45
Si1403CDL-T1-GE3	SiA437DJ-T1-GE3	SiS990DN-T1-GE3	SM5S20AHE3/2D
Si1416EDH-T1-GE3	SiA440DJ-T1-GE3	SiSA14DN-T1-GE3	SM5S22AHE3/2D
Si1469DH-T1-GE3	SiA446DJ-T1-GE3	SJ1-3515N	SM5S26AHE3/2D
Si2302DS	SiA462DJ-T1-GE3	SL05T1G	SM5S33AHE3/2D
Si2304DS	SiA906EDJ-T1-GE3	SL12-E3/5AT	SM5S36AHE3/2D
Si2372DS-T1-GE3	SiA914ADJ-T1-GE3	SL13-E3/61T	

Multisim 14.0 Full Components

SM6S33AHE3/2D	SMAJ26A-E3/61	SMBJ5.0CA-E3/52	SMCJ28CA-E3/57T
SM6T12A-E3/52	SMAJ28CA-E3/61	SMBJ58A-E3/52	SMCJ30CA-E3/57T
SM8S12AHE3/2D	SMAJ36A-E3/61	SMBJ58CA-E3/52	SMCJ33CA-E3/57T
SM8S14AHE3/2D	SMAJ40CA-E3/61	SMBJ6.0A-E3/52	SMCJ36CA-E3/57T
SM8S15AHE3/2D	SMAJ530-E3/61	SMBJ70A-E3/52	SMCJ48CA-E3/57T
SM8S16AHE3/2D	SMAJ6.5A-E3/61	SMBJ8.0A-E3/52	SMCJ5.0CA-E3/57T
SM8S17AHE3/2D	SMAJ60A-E3/61	SMBJ8.0CA-E3/52	SMCJ51CA-E3/57T
SM8S18AHE3/2D	SMBJ28CA-E3/52	SMBJ85A-E3/52	SMCJ58A-E3/57T
SM8S22AHE3/2D	SMBJ14A-E3/52	SMBT2222A	SMCJ6.5A-E3/57T
SM8S24AHE3/2D	SMBJ15CA-E3/52	SMBT2907A	SMCJ75A-E3/57T
SM8S26AHE3/2D	SMBJ170A-E3/52	SMBT35200MT1G	SMCJ78A-E3/57T
SM8S30AHE3/2D	SMBJ188CA-E3/52	SMBT3906	SMCJ8.5A-E3/57T
SM8S33AHE3/2D	SMBJ22A-E3/52	SMBT3946DW1T1G	SMF05CT1G
SM8S36AHE3/2D	SMBJ24CA-E3/52	SMBTA06	SMF05CT2G
SM8S43AHE3/2D	SMBJ26CA-E3/52	SMBTA42	SMF12AT1G
SMA5J28A-E3/61	SMBJ28CA-E3/52	SMBTA56C	SMF12CT1G
SMAJ11A-E3/61	SMBJ30A-E3/52	SMBTA92	SMF15CT1G
SMAJ11CA-E3/61	SMBJ33A-E3/52	SMCJ12A-E3/57T	SMF18AT1G
SMAJ12A-E3/61	SMBJ33CA-E3/52	SMCJ130CA-E3/57T	SMF22AT1G
SMAJ12CA-E3/61	SMBJ36A-E3/52	SMCJ15A-E3/57T	SMF24AT1G
SMAJ150CA-E3/61	SMBJ36CA-E3/52	SMCJ15CA-E3/57T	SMF24CT1G
SMAJ15A-E3/61	SMBJ3V3-E3/52	SMCJ16CA-E3/57T	SMF26AT1G
SMAJ16A-E3/61	SMBJ45A-E3/52	SMCJ18A-E3/57T	SMF28AT1G
SMAJ24A-E3/61	SMBJ48A-E3/52	SMCJ18CA-E3/57T	SMF30AT1G
SMAJ24CA-E3/61	SMBJ48CA-E3/52	SMCJ26CA-E3/57T	SMF33AT1G

Multisim 14.0 Full Components

SMF36AT1G	SML4751	SMMBT3904TT1G	SMMUN2116LT1G
SMF48AT1G	SML4752	SMMBT4401LT1G	SMMUN2116LT3G
SMF5.0AT1G	SML4753	SMMBT4403LT1G	SMMUN2134LT1G
SMF58AT1G	SML4754	SMMBT5401LT1G	SMMUN2211LT1G
SMF6.0AT1G	SML4755	SMMBT5551LT1G	SMMUN2211LT3G
SMF6.5AT1G	SML4756	SMMBT5551LT3G	SMMUN2213LT1G
SMF7.0AT1G	SML4757	SMMBTA06LT1G	SMMUN2213LT3G
SMF7.5AT1G	SML4758	SMMBTA06LT3G	SMMUN2214LT1G
SMF8.0AT1G	SML4759	SMMBTA06WT1G	SMMUN2215LT1G
SML4735	SML4760	SMMBTA14LT1G	SMMUN2216LT1G
SML4736	SML4761	SMMBTA42LT1G	SMMUN2216LT3G
SML4737	SML4762	SMMBTA42LT3G	SMMUN2233LT1G
SML4738	SML4763	SMMBTA56LT1G	SMMUN2234LT1G
SML4739	SMMBD2837LT1G	SMMBTA56LT3G	SMS05T1G
SML4740	SMMBD301LT3G	SMMBTA92LT1G	SMUN2111T1G
SML4741	SMMBD7000LT1G	SMMBTA92LT3G	SMUN2111T3G
SML4742	SMMBD7000LT3G	SMMDL914T1G	SMUN2114T1G
SML4743	SMMBD914LT1G	SMMJT350T1G	SMUN2211T1G
SML4744	SMMBD914LT3G	SMMSD301T1G	SMUN2211T3G
SML4745	SMMBT2222ALT1G	SMMSD4148T1G	SMUN2216T1G
SML4746	SMMBT2222ALT3G	SMMSD4148T3G	SMUN2230T1G
SML4747	SMMBT2369ALT1G	SMMUN2111LT1G	SMUN2232T1G
SML4748	SMMBT2907ALT1G	SMMUN2111LT3G	SMUN2240T1G
SML4749	SMMBT2907ALT3G	SMMUN2113LT1G	SMUN5112DW1T1
SML4750	SMMBT3904LT1G	SMMUN2114LT1G	G

Multisim 14.0 Full Components

SMUN5112T1G	SMUN5232DW1T1 G	SN7002N	SPA12N50C3
SMUN5113DW1T1 G	SMUN5232T1G	SN7002W	SPA15N60C3
SMUN5113T1G	SMUN5233DW1T1 G	SN74121N	SPA15N60CFD
SMUN5114DW1T1 G	SMUN5233T1G	SN74123D	SPA16N50C3
SMUN5114T1G	SMUN5235DW1T1 G	SN74123FK	SPA17N80C3
SMUN5115DW1T1 G	SMUN5237DW1T1 G	SN74123N	SPA20N60C3
SMUN5115T1G	SMUN5311DW1T2 G	SN74130N	SPA20N60CFD
SMUN5116DW1T1 G	SMUN5312DW1T1 G	SNSS30201MR6T1G	SPA21N50C3
SMUN5133T1G	SMUN5313DW1T1 G	SNSS35200MR6T1G	SPB02N60C3
SMUN5211T1G	SMUN5314DW1T1 G	SNSS40600CF8T1G	SPB02N60S5
SMUN5211T3G	SMUN5315DW1T1 G	SONALERT	SPB03N60C3
SMUN5212T1G	SMUN5330DW1T1 G	SPA02N80C3	SPB03N60S5
SMUN5213DW1T1 G	SMUN5335DW1T1 G	SPA03N60C3	SPB04N50C3
SMUN5213T1G	SN10502D	SPA04N50C3	SPB04N60C3
SMUN5214DW1T1 G	SN10502DGK	SPA04N60C3	SPB04N60S5
SMUN5214T1G	SN10502DGN	SPA04N80C3	SPB07N60C3
SMUN5215T1G	SN200501036DRE4	SPA06N60C3	SPB07N60S5
SMUN5216DW1T1 G	SN412008DRE4	SPA06N80C3	SPB08P06P G
SMUN5230DW1T1 G		SPA07N60C3	SPB100N03S2-03 G
		SPA07N60CFD	SPB11N60C3
		SPA08N50C3	SPB11N60S5
		SPA08N80C3	SPB12N50C3
		SPA11N60C3	SPB16N50C3
		SPA11N60CFD	SPB17N80C3
		SPA11N80C3	SPB18P06P G

Multisim 14.0 Full Components

SPB20N60C3	SPD15P10PL G	SPI20N60C3	SPP15N60C3
SPB20N60S5	SPD18P06P G	SPI20N60CFD	SPP15N60CFD
SPB21N50C3	SPD30N03S2L-07 G	SPI21N50C3	SPP15P10P H
SPB80P06P G	SPD30N03S2L-10 G	SPP02N60C3	SPP15P10PL H
SPD01N60C3	SPD30N03S2L-20 G	SPP02N60S5	SPP16N50C3
SPD02N50C3	SPD30P06P G	SPP02N80C3	SPP17N80C3
SPD02N60C3	SPD50N03S2-07 G	SPP03N60C3	SPP18P06P H
SPD02N60S5	SPD50N03S2L-06 G	SPP03N60S5	SPP20N60C3
SPD02N80C3	SPD50P03L G	SPP04N50C3	SPP20N60CFD
SPD03N50C3	SPDT	SPP04N60C3	SPP20N60S5
SPD03N60C3	SPDT_CLOSED	SPP04N60S5	SPP21N50C3
SPD03N60S5	SPDT_OPEN	SPP04N80C3	SPP24N60C3
SPD04N50C3	SPEED_F	SPP06N60C3	SPP24N60CFD
SPD04N60C3	SPEED_FR	SPP06N80C3	SPP80P06P H
SPD04N60S5	SPI07N60C3	SPP07N60C3	SPST
SPD04N80C3	SPI07N60S5	SPP07N60CFD	SPST_CLOSED
SPD04P10PL G	SPI08N50C3	SPP07N60S5	SPST_NC_DB
SPD06N60C3	SPI08N80C3	SPP08N50C3	SPST_NC_SB
SPD06N80C3	SPI11N60C3	SPP08N80C3	SPST_NO_DB
SPD07N60C3	SPI11N60CFD	SPP08P06P H	SPST_NO_SB
SPD07N60S5	SPI11N60S5	SPP11N60C3	SPST_OPEN
SPD08N50C3	SPI12N50C3	SPP11N60CFD	SPU01N60C3
SPD08P06P G	SPI15N60C3	SPP11N60S5	SPU02N60C3
SPD09P06PL G	SPI15N60CFD	SPP11N80C3	SPU02N60S5
SPD15P10P G	SPI16N50C3	SPP12N50C3	SPU03N60C3

Multisim 14.0 Full Components

SPU03N60S5	SPW47N60CFD	SS10P6-M3/86A	SS34
SPU04N60C3	SPW52N50C3	SS10PH10-M3/86A	SS34-E3/57T
SPU04N60S5	SPZT2222AT1G	SS14-E3/61T	SS35
SPU07N60C3	SPZT2907AT1G	SS16-E3/61T	SS36-E3/57T
SPU07N60S5	SPZT651T1G	SS16T3G	SS3P4HM3/84A
SPW07N60CFD	SQJ461EP-T1-GE3	SS1H10-E3/5AT	SS3P4LHM3/86A
SPW11N60C3	SQS482EN-T1-GE3	SS1P3L-M3/84A	SS3P6-E3/84A
SPW11N60CFD	SR_4BIDI	SS1P4L-M3/84A	SS5P10-M3/86A
SPW11N60S5	SR_4P_P_3SO	SS1P4-M3/84A	SS5P6-M3/86A
SPW11N80C3	SR_4P_P_INV	SS1P6L-E3/84A	SS8P3L-M3/86A
SPW12N50C3	SR_4S_P	SS22T3G	SS8PH10-M3/86A
SPW15N60C3	SR_8P_2S	SS24-E3/52T	SSA24-E3/61T
SPW15N60CFD	SR_8P_S	SS24S-E3/61T	SSA33L-E3/61T
SPW16N50C3	SR_8P_S_C	SS24T3	SSA34-E3/61T
SPW17N80C3	SR_8PS_S_AS_L	SS24T3G	SSC53L-E3/57T
SPW20N60C3	SR_8PS_S_SL	SS26-E3/52T	SSC54-E3/57T
SPW20N60CFD	SR_8S_P	SS26T3	SSM2017P
SPW20N60S5	SR_FF	SS26T3G	SSM2017S
SPW21N50C3	SR_FF_NEGSR	SS2H10-E3/2CT	SSM2135S
SPW24N60C3	SR_FF_POSSR	SS2P3L-M3/84A	SSM2212RZ
SPW24N60CFD	SR_LATCH	SS2P4-M3/84A	SSM2212RZ-R7
SPW32N50C3	SR_LATCH_NEGSR	SS2PH10-M3/84A	SSM2212RZ-RL
SPW35N60C3	SS0503SH-TL-E	SS32	SSRD8620CTRG
SPW35N60CFD	SS10P3-M3/86A	SS32-E3/57T	SSRD8620CTT4G
SPW47N60C3	SS10P4-M3/86A	SS33	SSRD8620CTT4RG

Multisim 14.0 Full Components

ST10F168-PQFP(144)	SURA8120T3G	SURS8205T3G	SZ1SMB24CAT3G
ST10F269T3-TQFP(144)	SURA8130T3G	SURS8210T3G	SZ1SMB26CAT3G
ST10R272L-TQFP(100)	SURA8140T3G	SURS8220T3G	SZ1SMB28AT3G
ST5771-1	SURA8160T3G	SURS8320T3G	SZ1SMB28CAT3G
ST7263B-SDIP(32)	SURA8210T3G	SURS8340T3G	SZ1SMB30AT3G
ST7263B-SO(34)	SURA8215T3G	SURS8360BT3G	SZ1SMB30CAT3G
STD110N02RT4G	SURA8220T3G	SURS8360T3G	SZ1SMB33CAT3G
STD24N06LT4G	SURA8240T3G	SZ1.5SMC15AT3G	SZ1SMB5.0AT3G
STD2955T4G	SURB1620CTT4G	SZ1.5SMC20AT3G	SZ1SMB58CAT3G
STD5406NT4G	SURD8320T4G	SZ1.5SMC33AT3G	SZ1SMB5918BT3G
STD5407NT4G	SURD8330T4G	SZ1.5SMC39AT3G	SZ1SMB5919BT3G
STEP_CURRENT	SURD8530T4G	SZ1.5SMC43AT3G	SZ1SMB5920BT3G
STEP_VOLTAGE	SURHB8840CTT4G	SZ1.5SMC62AT3G	SZ1SMB5921BT3G
STP32N06L	SURHD8560T4G	SZ1SMA30AT3G	SZ1SMB5922BT3G
SUD17N25-165-E3	SURHD8560W1T4G	SZ1SMA40CAT3G	SZ1SMB5924BT3G
SUR620CTT4G	SURHS8160T3G	SZ1SMA5913BT3G	SZ1SMB5925BT3G
SUR81520G	SURS340DT3G	SZ1SMA5918BT3G	SZ1SMB5927BT3G
SUR81560G	SURS360DBT3G	SZ1SMA5921BT3G	SZ1SMB5931BT3G
SUR83020PTG	SURS360DT3G	SZ1SMA5922BT3G	SZ1SMB5933BT3G
SUR83060PTG	SURS8105T3G	SZ1SMA5927BT3G	SZ1SMB5934BT3G
SUR8820G	SURS8110T3G	SZ1SMA5932BT3G	SZ1SMB5935BT3G
SUR8840G	SURS8115T3G	SZ1SMA5936BT3G	SZ1SMB5936BT3G
SURA8110T3G	SURS8120T3G	SZ1SMA5940BT3G	SZ1SMB5937BT3G
	SURS8140T3G	SZ1SMB14AT3G	SZ1SMB5939BT3G
	SURS8160T3G	SZ1SMB24AT3G	SZ1SMC36AT3G

Multisim 14.0 Full Components

SZBZX84B16LT1G	SZMM3Z10VT1G	SZMM5Z5V1T1G	SZMMBZ5240BLT1 G
SZBZX84C12LT1G	SZMM3Z12VST1G	SZMM5Z5V6ST1G	SZMMBZ5242BLT1 G
SZBZX84C15LT1G	SZMM3Z15VT1G	SZMM5Z5V6T1G	SZMMBZ5248BLT1 G
SZBZX84C15LT3G	SZMM3Z18VT1G	SZMM5Z6V2ST1G	SZMMBZ5254BLT1 G
SZBZX84C33LT1G	SZMM3Z20VT1G	SZMM5Z6V8ST1G	SZMMBZ5256BLT1 G
SZBZX84C33LT3G	SZMM3Z2V4T1G	SZMM5Z6V8T1G	SZMMBZ5256BLT1 G
SZBZX84C36LT1G	SZMM3Z3V3ST1G	SZMM5Z7V5T1G	SZMMBZ5256BLT1 G
SZBZX84C3V0LT1G	SZMM3Z3V6T1G	SZMM5Z8V2ST1G	SZMMBZ5V6ALT1G
SZBZX84C4V7LT1G	SZMM3Z43VT1G	SZMM5Z8V2T1G	SZMMQA15VT1G
SZBZX84C4V7LT3G	SZMM3Z4V3ST1G	SZMMBZ15VDLT1G	SZMMQA5V6T1G
SZBZX84C5V1LT1G	SZMM3Z4V7T1G	SZMMBZ15VDLT3G	SZMMQA6V2T1G
SZBZX84C5V1LT3G	SZMM3Z5V1T1G	SZMMBZ20VALT1G	SZMMSZ10T1G
SZBZX84C5V6LT1G	SZMM3Z5V6ST1G	SZMMBZ27VALT1G	SZMMSZ12T1G
SZBZX84C5V6LT3G	SZMM5Z10VT1G	SZMMBZ27VALT3G	SZMMSZ2V7T1G
SZBZX84C68LT1G	SZMM5Z12VT1G	SZMMBZ27VCLT1G	SZMMSZ3V3T1G
SZBZX84C6V2LT1G	SZMM5Z16VT1G	SZMMBZ33VALT1G	SZMMSZ4678T1G
SZBZX84C6V2LT3G	SZMM5Z18VT1G	SZMMBZ5221BLT1 G	SZMMSZ4683T1G
SZBZX84C6V8LT1G	SZMM5Z20VT1G	SZMMBZ5222BLT1 G	SZMMSZ4688T1G
SZBZX84C6V8LT3G	SZMM5Z24VT1G	SZMMBZ5231BLT1 G	SZMMSZ4689T1G
SZBZX84C75LT1G	SZMM5Z27VT1G	SZMMBZ5231BLT3 G	SZMMSZ4690T1G
SZBZX84C9V1LT1G	SZMM5Z36VT1G	SZMMBZ5232BLT1 G	SZMMSZ4690T3G
SZBZX84C9V1LT3G	SZMM5Z3V0T1G	SZMMBZ5232BLT1 G	SZMMSZ4691T1G
SZESD5Z5.0T1G	SZMM5Z3V3T1G	SZMMBZ5232BLT1 G	SZMMSZ4692T1G
SZESD5Z7.0T1G	SZMM5Z4V7ST1G		SZMMSZ4696T1G
SZESD9B5.0ST5G	SZMM5Z4V7ST5G		

Multisim 14.0 Full Components

SZMMSZ4699T1G	SZNUP1105LT1G	TC1410NCOA	TC1412EPA
SZMMSZ4705T1G	SZNUP1301ML3T1G	TC1410NCPA	TC1412EUA
SZMMSZ4715T1G	SZNUP2105LT1G	TC1410NEOA	TC1412NCOA
SZMMSZ5221BT1G	SZNUP4301MR6T1 G	TC1410NEPA	TC1412NCPA
SZMMSZ5225BT1G	SZNUP4304MR6T1 G	TC1410NEUA	TC1412NEOA
SZMMSZ5226BT1G	SZNUP4304MR6T1 G	TC1410NVUA	TC1412NEPA
SZMMSZ5228BT1G	SZNZ9F2V7ST5G	TC1411COA	TC1412NEUA
SZMMSZ5231BT1G	SZNZ9F6V2ST5G	TC1411CPA	TC4404COA
SZMMSZ5234BT1G	SZP6SMB15AT3G	TC1411EOA	TC4404CPA
SZMMSZ5235BT1G	SZP6SMB18AT3G	TC1411EPA	TC4404EOA
SZMMSZ5236BT1G	SZP6SMB20AT3G	TC1411EUA	TC4404EPA
SZMMSZ5239BT1G	SZP6SMB33AT3G	TC1411NCOA	TC4405COA
SZMMSZ5240BT1G	SZP6SMB43CAT3G	TC1411NCPA	TC4405CPA
SZMMSZ5242BT1G	SZP6SMB51AT3G	TC1411NEOA	TC4405EOA
SZMMSZ5242BT3G	SZP6SMB6.8AT3G	TC1411NEPA	TC4405EPA
SZMMSZ5243BT1G	SZP6SMB62AT3G	TC1411NEUA	TC4420CAT
SZMMSZ5245BT1G	SZSMF12CT1G	TC1411NVOA	TC4420COA
SZMMSZ5246BT1G	SZSMF33AT1G	TC1411NVPA	TC4420CPA
SZMMSZ5254BT1G	T_FF	TC1411NVUA	TC4420EMF
SZMMSZ5258BT1G	T_FF_NEGSR	TC1411VOA	TC4420EOA
SZMMSZ5258BT3G	TC1410COA	TC1411VPA	TC4420EPA
SZMMSZ5259BT1G	TC1410CPA	TC1411VUA	TC4420IJA
SZMMSZ5260BT1G	TC1410EOA	TC1412COA	TC4420MJA
SZMMSZ5262BT1G	TC1410EPA	TC1412CPA	TC4420VAT
SZMSQA6V1W5T2G	TC1410EUA	TC1412EOA	TC4420VMF

Multisim 14.0 Full Components

TC4420VOA	TC4423COE	TC4425COE	TC4427EUA713
TC4420VPA	TC4423CPA	TC4425CPA	TC4427VMF
TC4421AVMF	TC4423EOE	TC4425EOE	TC4427VOA
TC4421CAT	TC4423EPA	TC4425EPA	TC4427VUA
TC4421CPA	TC4423MJA	TC4425VMF	TC4428ACOA713
TC4421EMF713	TC4423VMF	TC4425VOE	TC4428AEJA
TC4421EPA	TC4423VOE	TC4425VPA	TC4428AEOA713
TC4421ESM	TC4423VPA	TC4426ACOA713	TC4428AMJA
TC4421MJA	TC4424AVMF	TC4426AEOA713	TC4428COA
TC4421VAT	TC4424AVOA	TC4426COA	TC4428CPA
TC4421VMF	TC4424AVOE	TC4426CPA	TC4428EMF
TC4421VPA	TC4424AVPA	TC4426EMF	TC4428EOA
TC4422CAT	TC4424COE	TC4426EOA	TC4428EPA
TC4422CPA	TC4424CPA	TC4426EPA	TC4428EUA
TC4422EAT	TC4424EMF	TC4426EUA	TC4428VMF
TC4422EPA	TC4424EOE	TC4426MJA	TC4428VOA
TC4422ESM	TC4424EPA	TC4426VMF	TC4428VUA
TC4422MJA	TC4424MJA	TC4426VUA	TC4429COA713
TC4422VAT	TC4424VMF	TC4427ACOA713	TC4429EMF
TC4422VMF	TC4424VOE	TC4427AEOA713	TC4429EOA713
TC4422VPA	TC4424VPA	TC4427COA	TC4429IJA
TC4423AVMF	TC4425AVMF	TC4427CPA	TC4429MJA
TC4423AVOA	TC4425AVOA	TC4427EMF	TC4429VAT
TC4423AVOE	TC4425AVOE	TC4427EOA	TC4429VMF
TC4423AVPA	TC4425AVPA	TC4427EPA	TC4429VOA

Multisim 14.0 Full Components

TC4429VPA	TC4468CPD	TDE1898C_SO20	TDZ6V2J
TC4431COA	TC4468EOE713	TDM_CURRENT	TDZ6V8J
TC4431CPA	TC4468MOE	TDM_VOLTAGE	TDZ7V5J
TC4431EOA	TC4469COE	TDZ10J	TDZ8V2J
TC4431EPA	TC4469CPD	TDZ11J	TDZ9V1J
TC4431VOA	TC4469EJD	TDZ12J	TEMD1000
TC4431VPA	TC4469MJD	TDZ13J	TEMD1020
TC4432COA	TCET1100	TDZ15J	TEMD1030
TC4432CPA	TCET1100G	TDZ16J	TEMD5010X01
TC4432EOA	TCET1600	TDZ18J	TEMD5020X01
TC4432EPA	TCET1600G	TDZ20J	TEMD5110X01
TC4432VOA	TCLT1003	TDZ22J	TEMD5510FX01
TC4432VPA	TCMT1103	TDZ24J	TEMD6010FX01
TC4451VAT	TCMT1600	TDZ27J	TEMP_NC
TC4451VMF	TCMT4600	TDZ2V4J	TEMP_NO
TC4451VOA	TD_SW1	TDZ2V7J	TEMPLATE_1P1S_T MODEL
TC4451VPA	TDA2030	TDZ30J	TEMPLATE_1P2S_C OUPLED
TC4452VAT	TDE1890_SO20	TDZ3V0J	TEMPLATE_1P2S_N ON_LINEAR
TC4452VMF	TDE1890_ZIP11	TDZ3V3J	TEMPLATE_1P2S_T AP_TMODEL
TC4452VOA	TDE1891_SIP11	TDZ3V6J	TEMPLATE_1P2S_T MODEL
TC4452VPA	TDE1891_ZIP11	TDZ3V9J	TEST_LABEL
TC4467COE	TDE1897C_DIP8	TDZ4V3J	TEST_PT_SMT
TC4467CPD	TDE1897C_SO20	TDZ4V7J	
TC4467EOE713	TDE1898C_DIP8	TDZ5V1J	
TC4468COE	TDE1898C_SIP9	TDZ5V6J	

Multisim 14.0 Full Components

TEST_PT_THT	THS3111CDGNR	THS4001ID	THS4032IDGN
THERMAL_NOISE	THS3111DGN	THS4011CD	THS4041CD
THERMAL_OL	THS3111ID	THS4011CDGN	THS4041CDGN
THERMAL_OL_RELAY	THS3111IDGN	THS4011ID	THS4041ID
THREE_PHASE_DELTA	THS3120CDGN	THS4011MFKB	THS4041IDGN
THREE_PHASE_WYE	THS3120DGN	THS4012CD	THS4042CD
THS3001CD	THS3120ID	THS4012CDGN	THS4042CDGN
THS3001CDGN	THS3120IDGN	THS4012ID	THS4042ID
THS3001ID	THS3121CD	THS4021CD	THS4042IDGN
THS3001IDGN	THS3121ID	THS4021CDGN	THS4051CD
THS3061D	THS3121IDGN	THS4021ID	THS4051CDGN
THS3061DGN	THS3122CD	THS4021IDGN	THS4051ID
THS3062D	THS3122CDDA	THS4022CD	THS4051IDGN
THS3062DDA	THS3122ID	THS4022CDGN	THS4051MFK
THS3062DGN	THS3122IDDA	THS4022ID	THS4051MJG
THS3091D	THS3125CPWP	THS4022IDGN	THS4052CD
THS3091DDA	THS3125ID	THS4031CD	THS4052CDGN
THS3095D	THS3125IPWP	THS4031CDGN	THS4052ID
THS3095DDA	THS3201D	THS4031ID	THS4052IDGN
THS3110DGN	THS3201DBVT	THS4031IDGN	THS4061CD
THS3110ID	THS3201DGK	THS4031MFK	THS4061CDGN
THS3110IDGN	THS3202D	THS4031MJG	THS4061ID
THS3110IDR	THS3202DGK	THS4032CD	THS4061IDGN
THS3111CD	THS3202DGN	THS4032CDGN	THS4061MFK
	THS4001CD	THS4032ID	THS4061MJG

Multisim 14.0 Full Components

THS4062CD	THS4140CDGK	THS4221DGN	THS4500IDGK
THS4062CDGN	THS4140ID	THS4222D	THS4500IDGN
THS4062ID	THS4140IDGK	THS4222DGK	THS4501CD
THS4062IDGN	THS4141CD	THS4222DGN	THS4501CDGK
THS4081CD	THS4141CDGK	THS4225D	THS4501CDGN
THS4081CDGN	THS4141ID	THS4225DGK	THS4501ID
THS4081ID	THS4141IDGK	THS4225DGN	THS4501IDGK
THS4081IDGN	THS4150CD	THS4226DGQ	THS4501IDGN
THS4082CD	THS4150CDGK	THS4271D	THS4502CD
THS4082CDGN	THS4150ID	THS4271DGK	THS4502CDGK
THS4082ID	THS4150IDGK	THS4271DGN	THS4502ID
THS4082IDGN	THS4151CD	THS4271DR	THS4502IDGK
THS4120CD	THS4151CDGK	THS4271DRBT	THS4503CD
THS4120CDGK	THS4151ID	THS4281D	THS4503CDGK
THS4121CD	THS4151IDGK	THS4281DBVR	THS4503CDGN
THS4121CDGK	THS4211D	THS4281DGK	THS4503ID
THS4130CD	THS4211DGK	THS4302RGTT	THS4503IDGK
THS4130CDGK	THS4211DGN	THS4303RGTT	THS4503IDGN
THS4130ID	THS4215D	THS4304D	THS4505D
THS4130IDGK	THS4215DGK	THS4304DBVT	THS4505DGK
THS4131CD	THS4215DGN	THS4304DGK	THS4508RGTR
THS4131CDGK	THS4215DRBT	THS4500CD	THS4509RGT
THS4131ID	THS4221D	THS4500CDGK	THS4511RGTT
THS4131IDGK	THS4221DBV	THS4500CDGN	THS4513RGTR
THS4140CD	THS4221DGK	THS4500ID	THS4520RGTR

Multisim 14.0 Full Components

THS4601CD	THS6043ID	THS6182DWP	TIP101G
THS4601CDDA	THS6043IPWP	THS6182RHFR	TIP102G
THS4601CDG4	THS6052CD	THS6184PWP	TIP106G
THS4601ID	THS6052CDDA	THS6184RHFR	TIP107G
THS4601IDDA	THS6052ID	THS7001CPWP	TIP110G
THS4601IDG4	THS6052IDDA	THS7001IPWP	TIP111G
THS4631D	THS6053CPWPR	THS7002CPWP	TIP112G
THS4631DDA	THS6053ID	THS7002IPWP	TIP115G
THS4631DGN	THS6053IPWP	THS7530PWP	TIP116G
THS6002CDWP	THS6062CD	TIME_DELAY_1A	TIP117G
THS6002IDWP	THS6062CDGN	TIME_DELAY_1C	TIP120G
THS6007IPWP	THS6062ID	TIME_DELAY_2A	TIP121G
THS6012CDWP	THS6062IDGN	TIME_DELAY_2C	TIP122G
THS6012IDWP	THS6072CD	TIME_DELAY_3A	TIP125G
THS6012IGQER	THS6072CDGN	TIME_DELAY_3C	TIP126G
THS6022CPWP	THS6072ID	TIME_DELAY_4A	TIP127G
THS6022IPWP	THS6072IDGNR	TIME_DELAY_4C	TIP140G
THS6032CDWP	THS6092CDDA	TIME_DELAY_NC	TIP141G
THS6032IDWP	THS6092ID	TIME_DELAY_NO	TIP142G
THS6032IVFPG4	THS6092IDDA	TIMED_NCTC	TIP147G
THS6042CDDA	THS6093CPWP	TIMED_NCTO	TIP2955G
THS6042ID	THS6093ID	TIMED_NOTC	TIP29AG
THS6042IDDA	THS6093IPWP	TIMED_NOTO	TIP29BG
THS6043CD	THS6182D	TI-MSP430-HDR	TIP29CG
THS6043CPWP	THS6182DW	TIP100G	TIP3055G

Multisim 14.0 Full Components

TIP30CG	TIS93	TL032AID	TL034CN
TIP31AG	TIS97	TL032AIP	TL034ID
TIP31BG	TIS98	TL032AMD	TL034IN
TIP31CG	TIS99	TL032AMFK	TL034MD
TIP31G	TL022CD	TL032AMJG	TL034MFK
TIP32AG	TL022CP	TL032AMJL	TL034MJ
TIP32BG	TL022MJG	TL032AMP	TL034MN
TIP32CG	TL022MU	TL032CD	TL044CJ
TIP32G	TL031ACD	TL032CP	TL044CN
TIP33CG	TL031ACP	TL032ID	TL044MFK
TIP35AG	TL031AID	TL032IP	TL044MJ
TIP35CG	TL031AIP	TL032MD	TL044MW
TIP36AG	TL031AMD	TL032MFK	TL051ACD
TIP36CG	TL031AMFK	TL032MJG	TL051ACP
TIP41AG	TL031AMJG	TL032ML	TL051AID
TIP41BG	TL031AML	TL032MP	TL051AIP
TIP41CG	TL031AMP	TL034ACD	TL051AMD
TIP42AG	TL031ID	TL034ACN	TL051AMFK
TIP42BG	TL031IP	TL034AID	TL051AMJG
TIP42CG	TL031MD	TL034AIN	TL051AML
TIP42G	TL031MFK	TL034AMD	TL051AMP
TIP47G	TL031MJG	TL034AMFK	TL051CD
TIP48G	TL031MP	TL034AMJ	TL051CP
TIP50G	TL032ACD	TL034AMN	TL051ID
TIS92	TL032ACP	TL034CD	TL051IP

Multisim 14.0 Full Components

TL051MD	TL054AID	TL061MU	TL064CNSR
TL051MFK	TL054AIN	TL061VD	TL064CPW
TL051MJG	TL054AMD	TL061VP	TL064ID
TL051ML	TL054AMFK	TL062ACD	TL064IN
TL051MP	TL054AMJ	TL062ACP	TL064MFK
TL052ACD	TL054AMN	TL062ACPSR	TL064MJ
TL052ACP	TL054CD	TL062BCD	TL064MW
TL052AID	TL054CN	TL062BCP	TL066ACD
TL052AIP	TL054ID	TL062CD	TL066ACP
TL052AMD	TL054IN	TL062CP	TL066CD
TL052AMFK	TL054MD	TL062CPSR	TL066CP
TL052AMJG	TL054MFK	TL062CPW	TL066ID
TL052AML	TL054MJ	TL062ID	TL066IP
TL052AMP	TL054MN	TL062IP	TL066MFK
TL052CD	TL061ACD	TL062IPW	TL066MJG
TL052CP	TL061ACP	TL062MFK	TL070ACD
TL052ID	TL061BCD	TL062MJG	TL070ACJG
TL052IP	TL061BCP	TL062ML	TL070ACP
TL052MD	TL061CD	TL062MU	TL070CD
TL052MFK	TL061CP	TL064ACD	TL070CJG
TL052MJG	TL061ID	TL064ACN	TL070CP
TL052ML	TL061IP	TL064BCD	TL070CPW
TL052MP	TL061MFK	TL064BCN	TL070ID
TL054ACD	TL061MJG	TL064CD	TL070IJG
TL054ACN	TL061ML	TL064CN	TL070IP

Multisim 14.0 Full Components

TL070MD	TL072CPWLE	TL080M	TL082MJG
TL070MP	TL072ID	TL081ACD	TL083
TL071ACD	TL072IP	TL081ACJG	TL084ACD
TL071ACJG	TL072MFK	TL081ACP	TL084ACN
TL071ACP	TL072MJG	TL081AMJG	TL084ACNSR
TL071BCD	TL072MJGB	TL081BCD	TL084BCD
TL071BCP	TL072ML	TL081BCJG	TL084BCN
TL071CD	TL072MP	TL081BCP	TL084CD
TL071CJG	TL074ACD	TL081CD	TL084CN
TL071CP	TL074ACN	TL081CJG	TL084CNSR
TL071CPWLE	TL074BCD	TL081CP	TL084CPW
TL071ID	TL074BCN	TL081CPW	TL084ID
TL071IP	TL074CD	TL081ID	TL084IN
TL071MFK	TL074CN	TL081IJG	TL084MFK
TL071MJG	TL074CPWLE	TL081IP	TL084MJ
TL071ML	TL074ID	TL081MFK	TL085
TL072ACD	TL074IN	TL081MJG	TL087CD
TL072ACP	TL074MFK	TL081MU	TL087CJG
TL072ACPSR	TL074MJ	TL082CD	TL087CL
TL072BCD	TL074MN	TL082CM	TL087CP
TL072BCP	TL074MW	TL082CP	TL087ID
TL072CD	TL075	TL082ID	TL087IJG
TL072CP	TL075CN	TL082IP	TL087IL
TL072CPSR	TL080CD	TL082IPWR	TL087IP
TL072CPW	TL080CP	TL082MFK	TL088CD

Multisim 14.0 Full Components

TL088CJG	TL321ID	TL431ACD	TLC070IP
TL088CL	TL321IP	TL431ACLP	TLC071CD
TL088CP	TL322CD	TL431ACP	TLC071CP
TL088ID	TL322CDR	TL431BCD	TLC071ID
TL088IJG	TL322CP	TL431BCLP	TLC071IP
TL088IL	TL322ID	TL431BCP	TLC074CD
TL088IP	TL322IP	TL431ID	TLC074CN
TL088MJG	TL33071D	TL431IDBVR	TLC074CPWP
TL088ML	TL33071P	TL431IDBZR	TLC081CD
TL088MU	TL331IDBVR	TL431ILP	TLC081CP
TL136	TL331KDBVR	TL431ILPR	TLC081ID
TL136N	TL34071D	TL431IP	TLC081IP
TL287CD	TL34071P	TL431IPK	TLC1078CD
TL287CJG	TL3472CD	TL431QD	TLC1078CP
TL287CL	TL3472CP	TL431QDBVR	TLC1078ID
TL287CP	TL3472ID	TL431QDBZR	TLC1078IP
TL288CD	TL3472IP	TL431QDCKR	TLC1078MD
TL288CJG	TL3474CD	TL431QPK	TLC1078MFK
TL288CL	TL3474CN	TL972ID	TLC1078MJG
TL288CP	TL3474CPW	TL972IDGKR	TLC1078MP
TL288MJG	TL3474ID	TL972IP	TLC1079CD
TL288ML	TL3474IN	TL972IPW	TLC1079CN
TL288MU	TL3474IPW	TLC070CD	TLC1079ID
TL321CD	TL35071D	TLC070CP	TLC1079IN
TL321CP	TL35071P	TLC070ID	TLC1079MD

Multisim 14.0 Full Components

TLC1079MFK	TLC2202BCP	TLC2254MJ	TLC2274CN
TLC1079MJ	TLC2202BID	TLC2254MW	TLC2274CPWLE
TLC1079MN	TLC2202BIP	TLC2262CD	TLC2274MD
TLC2201ACD	TLC2202CD	TLC2262CP	TLC2274MFK
TLC2201ACP	TLC2202CP	TLC2262CPWLE	TLC2274MJ
TLC2201AID	TLC2202ID	TLC2262MFK	TLC2274MN
TLC2201AIP	TLC2202IP	TLC2262MJG	TLC251ACD
TLC2201BCD	TLC2202MD	TLC2262MU	TLC251ACP
TLC2201BCP	TLC2202MFK	TLC2264CD	TLC251BCD
TLC2201BID	TLC2202MJG	TLC2264CN	TLC251BCP
TLC2201BIP	TLC2202MP	TLC2264CPW	TLC251CD
TLC2201CD	TLC2202Y	TLC2264CPWLE	TLC251CP
TLC2201CP	TLC2252AID	TLC2264MFK	TLC251Y
TLC2201ID	TLC2252AIP	TLC2264MJ	TLC252ACD
TLC2201IP	TLC2252AIPWLE	TLC2264MW	TLC252ACP
TLC2201MD	TLC2252CD	TLC2272ACD	TLC252ACPW
TLC2201MFK	TLC2252CP	TLC2272ACP	TLC252BCD
TLC2201MJG	TLC2252CPWLE	TLC2272CD	TLC252BCP
TLC2201MP	TLC2252MFK	TLC2272CP	TLC252BCPW
TLC2201Y	TLC2252MJG	TLC2272CPWLE	TLC252CD
TLC2202ACD	TLC2252MU	TLC2272Y	TLC252CP
TLC2202ACP	TLC2254CD	TLC2274ACD	TLC252CPW
TLC2202AID	TLC2254CN	TLC2274ACN	TLC254ACD
TLC2202AIP	TLC2254CPWLE	TLC2274ACPW	TLC254ACN
TLC2202BCD	TLC2254MFK	TLC2274CD	TLC254BCD

Multisim 14.0 Full Components

TLC254BCN	TLC2652AI-8D	TLC2652Y	TLC2654M-14D
TLC254CD	TLC2652AIN	TLC2654AC-14D	TLC2654M-8D
TLC254CN	TLC2652AIP	TLC2654AC-8D	TLC2654MFK
TLC254CPW	TLC2652AM-14D	TLC2654ACN	TLC2654MJ
TLC25L2ACD	TLC2652AM-8D	TLC2654ACP	TLC2654MJG
TLC25L2ACP	TLC2652AMFK	TLC2654AI-14D	TLC2654MN
TLC25L2BCD	TLC2652AMJ	TLC2654AID	TLC2654MP
TLC25L2BCP	TLC2652AMJG	TLC2654AIN	TLC271ACD
TLC25L2CD	TLC2652AMN	TLC2654AIP	TLC271ACP
TLC25L2CP	TLC2652AMP	TLC2654AM-14D	TLC271AID
TLC25L4CD	TLC2652C-14D	TLC2654AM-8D	TLC271AIP
TLC25L4CN	TLC2652C-8D	TLC2654AMF	TLC271BCD
TLC25M2ACD	TLC2652CN	TLC2654AMFK	TLC271BCP
TLC25M2ACP	TLC2652CP	TLC2654AMJ	TLC271BID
TLC25M2BCD	TLC2652I-14D	TLC2654AMJG	TLC271BIP
TLC25M2BCP	TLC2652ID	TLC2654AMN	TLC271CD
TLC25M2CD	TLC2652IN	TLC2654AMP	TLC271CP
TLC25M2CP	TLC2652IP	TLC2654C-14D	TLC271ID
TLC25M4CD	TLC2652M-14D	TLC2654C-8D	TLC271IP
TLC25M4CN	TLC2652M-8D	TLC2654CN	TLC271MD
TLC2652AC-14D	TLC2652MFK	TLC2654CP	TLC271MFK
TLC2652AC-8D	TLC2652MJ	TLC2654I-14D	TLC271MJG
TLC2652ACN	TLC2652MJG	TLC2654I-8D	TLC271MP
TLC2652ACP	TLC2652MN	TLC2654IN	TLC272CD
TLC2652AI-14D	TLC2652MP	TLC2654IP	TLC272CP

Multisim 14.0 Full Components

TLC272CPW	TLC279CN	TLC27L4AID	TLC27L9IN
TLC272ID	TLC279ID	TLC27L4AIN	TLC27L9MD
TLC272IP	TLC279IN	TLC27L4BCD	TLC27L9MFK
TLC272MD	TLC279MD	TLC27L4BCN	TLC27L9MJ
TLC272MFK	TLC279MFK	TLC27L4BID	TLC27L9MP
TLC272MJG	TLC279MJ	TLC27L4BIN	TLC27M2ACD
TLC272MP	TLC279MN	TLC27L4CD	TLC27M2ACP
TLC274CD	TLC27L2ACD	TLC27L4CN	TLC27M2AID
TLC274CN	TLC27L2ACP	TLC27L4ID	TLC27M2AIP
TLC274CPW	TLC27L2AID	TLC27L4IN	TLC27M2BCD
TLC274ID	TLC27L2AIP	TLC27L4MD	TLC27M2BCP
TLC274IN	TLC27L2BCD	TLC27L4MFK	TLC27M2BID
TLC274MD	TLC27L2BCP	TLC27L4MJ	TLC27M2BIP
TLC274MFK	TLC27L2BID	TLC27L4MN	TLC27M2CD
TLC274MJ	TLC27L2BIP	TLC27L7CD	TLC27M2CP
TLC274MN	TLC27L2CD	TLC27L7CP	TLC27M2ID
TLC277CD	TLC27L2CP	TLC27L7ID	TLC27M2IP
TLC277CP	TLC27L2ID	TLC27L7IP	TLC27M2MD
TLC277ID	TLC27L2IP	TLC27L7MD	TLC27M2MFK
TLC277IP	TLC27L2MD	TLC27L7MFK	TLC27M2MJG
TLC277MD	TLC27L2MFK	TLC27L7MJG	TLC27M2MP
TLC277MFK	TLC27L2MJG	TLC27L7MP	TLC27M4ACD
TLC277MJG	TLC27L2MP	TLC27L9CD	TLC27M4ACN
TLC277MP	TLC27L4ACD	TLC27L9CN	TLC27M4AID
TLC279CD	TLC27L4ACN	TLC27L9ID	TLC27M4AIN

Multisim 14.0 Full Components

TLC27M4BCD	TLC27M9MFK	TLC3702CP	TLC374CD
TLC27M4BCN	TLC27M9MJ	TLC3702ID	TLC374CN
TLC27M4BID	TLC27M9MN	TLC3702IP	TLC374CPW
TLC27M4BIN	TLC339CD	TLC3702MFK	TLC374ID
TLC27M4CD	TLC339CN	TLC3702MJG	TLC374IN
TLC27M4CN	TLC339ID	TLC3702QJG	TLC374MD
TLC27M4ID	TLC339IN	TLC3704CD	TLC374MFK
TLC27M4IN	TLC339MD	TLC3704CN	TLC374MJ
TLC27M4MD	TLC339MN	TLC3704CPW	TLC374MN
TLC27M4MFK	TLC339QD	TLC3704ID	TLC374QD
TLC27M4MJ	TLC339QN	TLC3704IN	TLC374QN
TLC27M4MN	TLC352CD	TLC3704MFK	TLC393CD
TLC27M7CD	TLC352CP	TLC3704MJ	TLC393CP
TLC27M7CP	TLC352ID	TLC3704QJ	TLC393ID
TLC27M7ID	TLC352IP	TLC372CD	TLC393IP
TLC27M7IP	TLC352MFK	TLC372CP	TLC393MD
TLC27M7MD	TLC352MJG	TLC372CPW	TLC393MFK
TLC27M7MFK	TLC354CD	TLC372ID	TLC393MJG
TLC27M7MJG	TLC354CN	TLC372IP	TLC393MP
TLC27M7MP	TLC354CPW	TLC372MD	TLC551CD
TLC27M9CD	TLC354ID	TLC372MFK	TLC551CP
TLC27M9CN	TLC354IN	TLC372MJG	TLC552C
TLC27M9ID	TLC354MD	TLC372MP	TLC552CD
TLC27M9IN	TLC354MN	TLC372QD	TLC552CN
TLC27M9MD	TLC3702CD	TLC372QP	TLC555CD

Multisim 14.0 Full Components

TLC555CP	TLE2021IP	TLE2024AMDW	TLE2027AMFK
TLC555CPSR	TLE2021MD	TLE2024AMFK	TLE2027AMJG
TLC555CPW	TLE2021MFK	TLE2024AMJ	TLE2027AML
TLC555ID	TLE2021MJG	TLE2024AMN	TLE2027AMP
TLC555IP	TLE2021MP	TLE2024BCDW	TLE2027CD
TLC555QDR	TLE2021Y	TLE2024BCN	TLE2027CP
TLC556CD	TLE2022ACD	TLE2024BIDW	TLE2027ID
TLC556CN	TLE2022ACP	TLE2024BIN	TLE2027IP
TLC556ID	TLE2022AID	TLE2024BMDW	TLE2027MD
TLC556IN	TLE2022AIP	TLE2024BMJ	TLE2027MFK
TLE2021ACD	TLE2022BCD	TLE2024BMN	TLE2027MJG
TLE2021ACP	TLE2022BCP	TLE2024CDW	TLE2027ML
TLE2021AID	TLE2022BID	TLE2024CN	TLE2027MP
TLE2021AIP	TLE2022BIP	TLE2024IDW	TLE2037ACD
TLE2021AMD	TLE2022CD	TLE2024IN	TLE2037ACP
TLE2021AMFK	TLE2022CDBLE	TLE2024MDW	TLE2037AID
TLE2021AMJG	TLE2022CP	TLE2024MFK	TLE2037AIP
TLE2021AMP	TLE2022CPWLE	TLE2024MJ	TLE2037AMD
TLE2021BI	TLE2022ID	TLE2024MN	TLE2037AMFK
TLE2021BMJG	TLE2022IP	TLE2024Y	TLE2037AMJG
TLE2021CD	TLE2022Y	TLE2027ACD	TLE2037AML
TLE2021CDBLE	TLE2024ACDW	TLE2027ACP	TLE2037AMP
TLE2021CP	TLE2024ACN	TLE2027AID	TLE2037CD
TLE2021CPWLE	TLE2024AIDW	TLE2027AIP	TLE2037CP
TLE2021ID	TLE2024AIN	TLE2027AMD	TLE2037ID

Multisim 14.0 Full Components

TLE2037IP	TLE2061CL	TLE2062BMFK	TLE2064CN
TLE2037MD	TLE2061CP	TLE2062BMJG	TLE2064ID
TLE2037MFK	TLE2061CPWLE	TLE2062BMP	TLE2064IN
TLE2037MJG	TLE2061ID	TLE2062CD	TLE2064MD
TLE2037ML	TLE2061IL	TLE2062CP	TLE2064MFK
TLE2037MP	TLE2061IP	TLE2062ID	TLE2064MJ
TLE2061ACD	TLE2061MD	TLE2062IP	TLE2064MN
TLE2061ACL	TLE2061MFK	TLE2062MD	TLE2064Y
TLE2061ACP	TLE2061MJG	TLE2062MFK	TLE2071CD
TLE2061AID	TLE2061ML	TLE2062MJG	TLE2071CP
TLE2061AIL	TLE2061MP	TLE2062MP	TLE2071MFK
TLE2061AIP	TLE2061Y	TLE2062Y	TLE2071MJG
TLE2061AMD	TLE2062ACD	TLE2064ACD	TLE2072CD
TLE2061AMFK	TLE2062ACP	TLE2064ACN	TLE2072CP
TLE2061AMJG	TLE2062AID	TLE2064AID	TLE2072MFK
TLE2061AML	TLE2062AIP	TLE2064AIN	TLE2074CN
TLE2061AMP	TLE2062AMD	TLE2064AMD	TLE2081CD
TLE2061BCL	TLE2062AMFK	TLE2064AMFK	TLE2081CP
TLE2061BIL	TLE2062AMJG	TLE2064AMJ	TLE2081MFK
TLE2061BIP	TLE2062AMP	TLE2064AMN	TLE2081MJG
TLE2061BMJG	TLE2062BCD	TLE2064BCN	TLE2082ACD
TLE2061BML	TLE2062BCP	TLE2064BIN	TLE2082ACP
TLE2061BMP	TLE2062BID	TLE2064BMJ	TLE2082AID
TLE2061CD	TLE2062BIP	TLE2064BMN	TLE2082AIP
TLE2061CDBLE	TLE2062BMD	TLE2064CD	TLE2082AMD

Multisim 14.0 Full Components

TLE2082AMFK	TLE2141MFK	TLE2144AMN	TLE2161CP
TLE2082AMJG	TLE2141MJG	TLE2144CDW	TLE2161ID
TLE2082AMP	TLE2141MP	TLE2144CN	TLE2161IP
TLE2082CD	TLE2141Y	TLE2144IDW	TLE2161MD
TLE2082CP	TLE2142ACD	TLE2144IN	TLE2161MFK
TLE2082ID	TLE2142ACP	TLE2144MDW	TLE2161MJG
TLE2082IP	TLE2142AID	TLE2144MFK	TLE2161ML
TLE2082MD	TLE2142AIP	TLE2144MJ	TLE2161MP
TLE2082MFK	TLE2142AMD	TLE2144MN	TLE2227ACP
TLE2082MJG	TLE2142AMFK	TLE2144Y	TLE2227CDW
TLE2082MP	TLE2142AMJG	TLE2161ACD	TLE2227CP
TLE2084CN	TLE2142AMP	TLE2161ACP	TLE2237ACP
TLE2141ACD	TLE2142CD	TLE2161AID	TLE2237CDW
TLE2141ACP	TLE2142CP	TLE2161AIP	TLE2237CP
TLE2141AID	TLE2142ID	TLE2161AMD	TLE2425CD
TLE2141AIP	TLE2142IP	TLE2161AMFK	TLE2425ID
TLE2141AMD	TLE2142MD	TLE2161AMJG	TLE2426CD
TLE2141AMFK	TLE2142MFK	TLE2161AML	TLE2426IP
TLE2141AMJG	TLE2142MJG	TLE2161AMP	TL-OP
TLE2141AMP	TLE2142MP	TLE2161BCP	TL-OP1
TLE2141CD	TLE2142Y	TLE2161BIP	TLV2211CDBV
TLE2141CP	TLE2144ACN	TLE2161BMJ	TLV2211IDBV
TLE2141ID	TLE2144AIN	TLE2161BML	TLV2221CDBV
TLE2141IP	TLE2144AMFK	TLE2161BMP	TLV2221IDBV
TLE2141MD	TLE2144AMJ	TLE2161CD	TLV2231CDBV

Multisim 14.0 Full Components

TLV2231IDBV	TLV2322ID	TLV2354IN	TLV2375ID
TLV2252ID	TLV2322IP	TLV2354IPW	TLV2375IN
TLV2252IP	TLV2322IPWLE	TLV2354MJ	TLV2375IPW
TLV2252MFK	TLV2324ID	TLV2361CDBV	TLV2401CD
TLV2252MJG	TLV2324IN	TLV2361IDBV	TLV2401CDBV
TLV2252MU	TLV2324IPWLE	TLV2362ID	TLV2401ID
TLV2254AID	TLV2332ID	TLV2362IDGK	TLV2401IDBV
TLV2254AIN	TLV2332IP	TLV2362IP	TLV2401IP
TLV2254AIPWLE	TLV2332IPWLE	TLV2362IPS	TLV2402CD
TLV2254ID	TLV2334ID	TLV2362IPW	TLV2402CDGK
TLV2254IN	TLV2334IN	TLV2370ID	TLV2402ID
TLV2254MFK	TLV2334IPWLE	TLV2370IDBV	TLV2402IDGK
TLV2254MJ	TLV2341ID	TLV2370IP	TLV2402IP
TLV2254QD	TLV2341IP	TLV2371ID	TLV2432AID
TLV2262AIPWLE	TLV2341IPWLE	TLV2371IDBV	TLV2432AIPW
TLV2262ID	TLV2342ID	TLV2371IP	TLV2432AMJG
TLV2262IP	TLV2342IP	TLV2372ID	TLV2434AID
TLV2262MFK	TLV2342IPWLE	TLV2372IDGK	TLV2434AIPW
TLV2262MJG	TLV2344ID	TLV2372IP	TLV2442CD
TLV2262MU	TLV2344IN	TLV2373ID	TLV2442CPW
TLV2264AIPWLE	TLV2344IPWLE	TLV2373IDGS	TLV2442MJG
TLV2264ID	TLV2352ID	TLV2373IN	TLV2444CD
TLV2264IN	TLV2352IP	TLV2374ID	TLV2444CPW
TLV2264MJ	TLV2352IPW	TLV2374IN	TLV2444ID
TLV2264QD	TLV2354ID	TLV2374IPW	TLV2444IPW

Multisim 14.0 Full Components

TLV2450AID	TLV2472AIP	TLV2760IDBV	TLV2785AIPW
TLV2450AIP	TLV2473AID	TLV2760IP	TLV3012AIDBVR
TLV2451AID	TLV2473AIP	TLV2761ID	TLV3012AIDCKR
TLV2451AIP	TLV2474AID	TLV2761IDBV	TLV3201AIDBVR
TLV2452AID	TLV2474AIN	TLV2761IP	TLV3201AIDCKR
TLV2452AIP	TLV2474AIPWP	TLV2762ID	TLV3202AID
TLV2453AID	TLV2475AID	TLV2762IDGK	TLV3202AIDGK
TLV2453AIN	TLV2475AIN	TLV2762IP	TLV3401CD
TLV2454AID	TLV2475AIPWP	TLV2763ID	TLV3401CDBVR
TLV2454AIN	TLV271CD	TLV2763IDGS	TLV3401ID
TLV2454AIPW	TLV271CDBVR	TLV2763IN	TLV3401IDBVR
TLV2455AID	TLV271ID	TLV2764ID	TLV3401IDG4
TLV2455AIN	TLV271IDBVR	TLV2764IN	TLV3401IP
TLV2455AIPW	TLV271IP	TLV2764IPW	TLV342ID
TLV2460CD	TLV272CD	TLV2765ID	TLV342IDGKR
TLV2460CDBV	TLV272CDGK	TLV2765IN	TLV342IRUGR
TLV2460CP	TLV272ID	TLV2765IPW	TLV3501AID
TLV2461CD	TLV272IDGK	TLV2772CD	TLV3501AIDBVR
TLV2461CDBV	TLV272IP	TLV2772CDGK	TLV3691IDCKR
TLV2461CP	TLV274CD	TLV2772CP	TLV3691IDPFR
TLV2470AID	TLV274CPW	TLV2782AID	TLV3701CD
TLV2470AIP	TLV274ID	TLV2783AID	TLV3701CDBVR
TLV2471AID	TLV274IN	TLV2784AID	TLV3701ID
TLV2471AIP	TLV274IPW	TLV2784AIPW	TLV3701IDBVR
TLV2472AID	TLV2760ID	TLV2785AID	TLV3701IP

Multisim 14.0 Full Components

TLV4110ID	TLV431ILPR	TMP90C801N	TPA301DR
TLV4110IDGNR	TLV431QPK	TMP94CM40F	TPS2811_SO8
TLV4110IP	TLVH431CDBVR	TMS320C6711B-100GFNA	TPS2812_SO8
TLV4111CD	TLVH431CDBZR	TMS320LC2402A-PAG(64)	TPS2813_SO8
TLV4111CDGN	TLVH431CDCKR	TMS320LC2402A-PG(64)	TPS2814_SO8
TLV4111ID	TLVH431CLP	TMS320LC2402A-PG(64)	TPS2815_SO8
TLV4111IDGN	TLVH431CLPR	TMS320LC2404A-PZ(100)	TPS2816_SOT23_5
TLV4112CD	TLVH431CPK	TMS320LC2406A-PZ(100)	TPS2817_SOT23_5
TLV4112CDGN	TLVH431IDBVR	TMS320LC2406A-PZ(100)	TPS2818_SOT23_5
TLV4112CP	TLVH431IDBZR	TMS320LF2402A-PG(64)	TPS2819_SOT23_5
TLV4112ID	TLVH431IDCKR	TMS320LF2403A-PAG(64)	TPS2828_SOT23_5
TLV4112IDGN	TLVH431ILP	TMS320LF2406A-PZ(100)	TPS2829_SOT23_5
TLV4112IP	TLVH431ILPR	TMS320LF2407A-PGE(144)	TPS2830_SO14
TLV4113CDGQR	TLVH431IPK	TN2219	TPS2831_SO14
TLV4113ID	TLVH431QDBVR	TN2219A	TPS2832_SO8
TLV4113IDGQ	TLVH431QDBZR	TN2905	TPS2833_SO8
TLV4113IN	TLVH431QDCKR	TN2905A	TPS2834_SO14
TLV431CDBVR	TLVH431QLP	TN4036	TPS2835_SO14
TLV431CDBZR	TLVH431QLPR	TOSHIBA-MIPS-HDR	TPS2836_SO8
TLV431CLP	TLVH431QPK	TPA301D	TPS2837_SO8
TLV431CLPM	TMP20AIDCKR	TPA301DGN	TPS2838_SO16
TLV431CLPR	TMP20AIDRLR		TPS2839_SO16
TLV431IDBVR	TMP90C800F		TPS2848_SO14
TLV431IDBZR	TMP90C800N		TPS2849_SO14
TLV431ILP	TMP90C801F		TPS5300_SO32

Multisim 14.0 Full Components

TPS60240_SO8	TPSMP18AHM3/84	TRIAC	UA709AMW
TPS60241_SO8	A	TRIANGULAR_CURR	UA709CD
TPS60242_SO8	TPSMP24AHM3/84	ENT	UA709CJG
TPS60243_SO8	A	TRIANGULAR_VOLT	UA709CP
TPS76150DBVR	TPSMP27AHE3/84A	AGE	UA709MJ
TPS780230300DRV	TPSMP30AHM3/84	TRIODE_VIRTUAL	UA709MU
R	A	TRISTATE	UA709MW
TPSMA16AHE3/61T	TPSMP36AHM3/84	TRISTATE_NEG	UA723CD
TPSMA20A/11T	A	TS_VIRTUAL	UA723CFK
TPSMA27AHE3/61T	TRAFFIC_LIGHT	TVP5145PFP-	UA723CJ
TPSMA30AHE3/61T	TRAFFIC_LIGHT_SINGLE	TQFP(80)	UA723CN
TPSMA33AHE3/61T	TRANSFER_FUNCTION_BLOCK	U257	UA723MU
TPSMA36AHE3/5AT	TRANSFORMER_CT	U308	UA741CD
TPSMB24AHE3/52T	_RATED	U309	UA741CP
TPSMB27A/2	TRANSFORMER_RATED	U310	UA741MFK
TPSMB30AHE3/52T	TRANSISTOR	U401	UA741MJ
TPSMB33AHE3/52T	TRANSISTOR_DELAY	U402	UA741MJG
TPSMB36A/5T	TRANSISTOR_DIODE	U403	UA741MU
TPSMB39A-E3/2T	E	U404	UA747CD
TPSMC22A-E3/57T	TRANSISTOR_DIODE_DELAY	U405	UA747CN
TPSMC27A-E3/57T	E_DELAY	U406	UA747MFK
TPSMC30AHE3_A/H	TRANSPORT_DELAY	U440	UA747MJ
TPSMC33A-E3/51T	TRF37A75IDSGR	U441	UA747MW
TPSMC36A/9AT	TRF37B75IDSGR	UA709AMJ	UA748CD
TPSMC39A-E3/57T	TRF37C75IDSGR	UA709AMJG	UA748CP
		UA709AMU	

Multisim 14.0 Full Components

UA748JG	UC3842A_DIP8	UCC27324_SO8	US1J-E3/5AT
UA748MJG	UC3842A_SO8	UCC27325_SO8	US1M-E3/61T
UA748MU	UC3842B_DIP8	UCC37323_SO8	UX60-MB-5ST
UC1705	UC3842B_SO8	UCC37324_SO8	V_REF1
UC1705_DIP8	UC3842T_DIP8	UCC37325_SO8	V_REF2
UC2705_DIP8	UC3842T_SO8	UF4002-E3/54	V_REF3
UC2842A_DIP8	UC3843A_DIP8	UF4007-E3/54	V_REF4
UC2842A_SO8	UC3843A_SO8	UF5406-E3/54	V_REF5
UC2842B_DIP8	UC3843B_DIP8	UG06D-E3/54	V10P10-M3/86A
UC2842B_SO8	UC3843B_SO8	UG1D-E3/54	V12P10-M3/86A
UC2843A_DIP8	UC3843T_DIP8	UG30DPT-E3/45	V8P10HM3/86A
UC2843A_SO8	UC3843T_SO8	UG5JT-E3/45	VARIABLE_CAPACIT OR
UC2843B_DIP8	UC3844A_DIP8	UG8DT-E3/45	VARIABLE_CAPACIT OR_RATED
UC2843B_SO8	UC3844A_SO8	UG8JCT-E3/45	VARIABLE_CAPACIT OR_VIRTUAL
UC2844A_DIP8	UC3844B_DIP8	UG8JTHE3/45	VARIABLE_INDUCT OR
UC2844A_SO8	UC3844B_SO8	ULN2001_DIP16	VARIABLE_INDUCT OR_RATED
UC2844B_DIP8	UC3844T_DIP8	ULN2001_SO16	VARIABLE_INDUCT OR_VIRTUAL
UC2844B_SO8	UC3844T_SO8	ULN2002_DIP16	VARIABLE_PULLUP_ VIRTUAL
UC2845A_DIP8	UC3845A_DIP8	ULN2002_SO16	VARIABLE_RESISTO R_VIRTUAL
UC2845A_SO8	UC3845A_SO8	ULN2003_DIP16	VBP104FAS
UC2845B_DIP8	UC3845B_DIP8	ULN2003_SO16	
UC2845B_SO8	UC3845B_SO8	ULN2004_DIP16	
UC3248	UC3845T_DIP8	ULN2004_SO16	
UC3705_DIP8	UC3845T_SO8	UNDCD_BARGRAPH	
UC3842	UCC27323_SO8	US1G-E3/61T	

Multisim 14.0 Full Components

VBP104FASR	VO2601-X007T	VO615A-3X017T	VOLTAGE_CONTROLLED_SQUARE_WAVE
VBPW34FAS	VO2601-X016	VO615A-3X018T	
VBPW34FASR	VO2601-X017T	VO615A-3X019T	VOLTAGE_CONTROLLED_TRIANGLE_WAVE
VBPW34S	VO2611	VOLTAGE_CONTROLLED_CAPACITOR_VIRTUAL	
VBPW34SR	VO2611-X006		VOLTAGE_CONTROLLED_VOLTAGE_SOURCE
VCA810AID	VO2611-X007T	VOLTAGE_CONTROLLED_CURRENT_SOURCE	
VCA810ID	VO2611-X016		VOLTAGE_DIFFERENTIATOR
VCA821ID	VO2611-X017T	VOLTAGE_CONTROLLED_DPDT	
VCA824ID	VO2630		VOLTAGE_GAIN_BLOCK
VCC	VO2630-X006	VOLTAGE_CONTROLLED_INDUCTOR_VIRTUAL	
VDAC	VO2630-X007T		VOLTAGE_HYSTeresis_BLOCK
VDAC16	VO2631	VOLTAGE_CONTROLLED_LIMITER	
VDD	VO2631-X006		VOLTAGE_INTEGRATOR
VEE	VO2631-X007T	VOLTAGE_CONTROLLED_PIECEWISE_LINEAR_SOURCE	
VN10LF	VO2631-X017T		VOLTAGE_SLEW_RATE_BLOCK
VO0600T	VO4661	VOLTAGE_CONTROLLED_RESISTOR_VIRTUAL	
VO0601T	VO4661-X006		VOLTAGE_SUMMER
VO0601-X001T	VO4661-X007T	VOLTAGE_CONTROLLED_SINE_WAVE	VOLTMETER_H
VO0611T	VO615A-3		VOLTMETER_HR
VO0630T	VO615A-3X001	VOLTAGE_CONTROLLED_SPDT	VOLTMETER_V
VO0631T	VO615A-3X006		VOLTMETER_VR
VO0631-X001T	VO615A-3X007T	VOLTAGE_CONTROLLED_SPST	VOM452T
VO0661T	VO615A-3X008T	VOLTAGE_CONTROLLED_SPST_ANIMATED	VOM453T
VO2601	VO615A-3X009T		VSS
VO2601-X006	VO615A-3X016		VTERM

Multisim 14.0 Full Components

W06G-E4/51	XC5202-4VQ64C	XC5206-4PQ100C	XCS05XL-4PC84C
WOBBLE_STICK	XC5202-5PC84C	XC5206-4TQ144C	XCS10-3PC84C
XC3020A-PQ100	XC5202-5PQ100C	XC5206-5PC84C	XCS10-4PC84C
XC3030A-PQ100	XC5202-5TQ144C	XC5206-5PQ100C	XCS10XL-4PC84C
XC3030A-VQ100	XC5202-5VQ64C	XC5206-5TQ144C	XCS20-3VQ100C
XC3030L-VQ100	XC5202-6PC84C	XC5206-6PC84C	XCS20-4VQ100C
XC3042A-PQ100	XC5202-6PQ100C	XC5206-6PQ100C	XCS20XL-4VQ100C
XC3042A-VQ100	XC5202-6TQ144C	XC5206-6TQ144C	XCS30-3VQ100C
XC3042L-VQ100	XC5202-6VQ64C	XC5210-3PC84C	XCS30-4VQ100C
XC3120A-PQ100	XC5204-3PC84C	XC5210-3TQ144C	XCS30XL-4VQ100C
XC3130A-PQ100	XC5204-3PQ100C	XC5210-4PC84C	XCS40-4PQ208C
XC3130A-VQ100	XC5204-3TQ144C	XC5210-4TQ144C	XCS40XL-4PQ208C
XC3142A-PQ100	XC5204-4PC84C	XC5210-5PC84C	XILINX-PARALLEL- III-IV-HDR
XC3142A-VQ100	XC5204-4PQ100C	XC5210-5TQ144C	
XC3142L-VQ100	XC5204-4TQ144C	XC5210-6PC84C	XILINX-PARALLEL- IV-HDR
XC4002XL-1PC84C	XC5204-5PC84C	XC5210-6TQ144C	XNOR2
XC4002XL-2PC84C	XC5204-5PQ100C	XC5215-3PQ160C	XNOR2
XC4002XL-3PC84C	XC5204-5TQ144C	XC5215-4PQ160C	XNOR3
XC5202-3PC84C	XC5204-6PC84C	XC5215-5PQ160C	XNOR3
XC5202-3PQ100C	XC5204-6PQ100C	XC5215-6PQ160C	XNOR4
XC5202-3TQ144C	XC5204-6TQ144C	XC9572XL- 10TQ100C	XNOR4
XC5202-3VQ64C	XC5206-3PC84C		XNOR5
XC5202-4PC84C	XC5206-3PQ100C	XC9572XL-7TQ100C	XNOR5
XC5202-4PQ100C	XC5206-3TQ144C	XCS05-3PC84C	XNOR6
XC5202-4TQ144C	XC5206-4PC84C	XCS05-4PC84C	XNOR6

Multisim 14.0 Full Components

XNOR7	Z4KE120A	Z84C00-DIP(40)	Z8S180-PLCC(68)
XNOR7	Z4KE130	Z84C00-PLCC(44)	Z8S180-QFP(80)
XNOR8	Z4KE130A	Z84C00-QFP(44)	ZC820
XNOR8	Z4KE140	Z84C10-DIP(40)	ZC821
XOR2	Z4KE140A	Z84C10-PLCC(44)	ZC822
XOR2	Z4KE150	Z84C15-QFP(100)	ZC823
XOR3	Z4KE150A	Z84C15-VQFP(100)	ZC824
XOR3	Z4KE160	Z84C20-DIP(40)	ZC825
XOR4	Z4KE160A	Z84C20-PLCC(44)	ZC826
XOR4	Z4KE170	Z84C30-DIP(28)	ZC830A
XOR5	Z4KE170A	Z84C30-PLCC(44)	ZC831A
XOR5	Z4KE180	Z84C30-QFP(44)	ZC832A
XOR6	Z4KE180A	Z84C40-DIP(40)	ZC833A
XOR6	Z4KE190	Z84C41-DIP(40)	ZC834A
XOR7	Z4KE190A	Z84C42-DIP(40)	ZC835A
XOR7	Z4KE200	Z84C43-QFP(44)	ZC836A
XOR8	Z4KE200A	Z84C44-PLCC(44)	ZDX1F
XOR8	Z80180-DIP(64)	Z84C90-LQFP(100)	ZDX2F
XTR300AIRGWR	Z80180-PLCC(68)	Z84C90-PLCC(84)	ZDX5
Z08470-DIP(40)	Z80180-QFP(80)	Z8L180-DIP(64)	ZENER
Z4KE100	Z80181-QFP(100)	Z8L180-PLCC(68)	ZGL41_100
Z4KE100A	Z80182-QFP(100)	Z8L180-QFP(80)	ZGL41_110
Z4KE110	Z80182-VQFP(100)	Z8L182-QFP(100)	ZGL41_120
Z4KE110A	Z80195-QFP(100)	Z8L182-VQFP(100)	ZGL41_130
Z4KE120	Z84015-QFP(100)	Z8S180-DIP(64)	ZGL41_140

Multisim 14.0 Full Components

ZGL41_150	ZPD4.7	ZTX237B	ZTX650
ZGL41_160	ZPD5.1	ZTX238	ZTX651
ZGL41_170	ZPD6.2	ZTX238B	ZTX653
ZGL41_180	ZPD6.8	ZTX239	ZTX657
ZGL41_190	ZPD7.5	ZTX239B	ZTX658
ZGL41_200	ZPD8.2	ZTX320	ZTX688B
ZPD10	ZTX1047A	ZTX321	ZTX689B
ZPD11	ZTX1048A	ZTX325	ZTX690B
ZPD12	ZTX1049A	ZTX327	ZTX692B
ZPD13	ZTX1051A	ZTX337A	ZTX694B
ZPD15	ZTX1053A	ZTX338A	ZTX696B
ZPD16	ZTX1055A	ZTX360	ZTX704
ZPD18	ZTX107	ZTX450	ZTX705
ZPD2.7	ZTX107B	ZTX454	ZTX718
ZPD20	ZTX108	ZTX455	ZTX749
ZPD22	ZTX108B	ZTX458	ZTX750
ZPD24	ZTX109	ZTX549	ZTX751
ZPD27	ZTX109B	ZTX550	ZTX753
ZPD3.0	ZTX212	ZTX558	ZTX757
ZPD3.3	ZTX212A	ZTX601B	ZTX758
ZPD3.6	ZTX213	ZTX604	ZTX788A
ZPD3.9	ZTX213A	ZTX605	ZTX788B
ZPD30	ZTX214	ZTX614	ZTX789A
ZPD33	ZTX214A	ZTX618	ZTX790A
ZPD4.3	ZTX237	ZTX649	ZTX792A

Multisim 14.0 Full Components

ZTX795A ZVP2106G

ZTX796A ZVP3306

ZTX849 ZVP4424A

ZTX851

ZTX869

ZTX948

ZTX949

ZTX951

ZTX953

ZTX955

ZTX956

ZTX957

ZTX958

ZTX968

ZVN0124A

ZVN2106A

ZVN2106G

ZVN3306A

ZVN3306F

ZVN3310F

ZVN4210G

ZVN4306G

ZVN4310G

ZVN4424G

ZVP2106A