

Multisim 14.0 Power Pro Components

741	1787386	1 mF [T510X108M004AT	1 mF [T520Y108M2R5AT
1028	1787580	E018]	E015]
1294	685119136923	1 mF	1 mF
2462	0.5_AMP	[T510X108M004AT	[T520Y108M2R5AT
2466	02BZ2.2	E023]	E025]
2468	02DZ4.7	1 mF	1 mF
2477	05AZ2.2	[T513E108M004AH	[T530X108M003AT
2481	1 mF	6110]	E010]
8051	[T491E108M004AT]	1 mF	1 mF
8052	1 mF	[T513X108M004AH	[T530X108M004AT
284258	[T491X108M004AT]	6110]	E006]
1708026	1 mF	1 mF	1 mF
1708039	[T494E108M004AT]	[T513X108M004AH	[T530X108M2R5AT
1708042	1 mF	6120]	E005]
1708055	[T494X108M004AT]	1 mF	1 mF
1708084	1 mF	[T520D108M2R5AT	[T530X108M2R5AT
1708110	[T495E108M004AT	E015]	E006]
1786837	E035]	1 mF	1 mF
1786866	1 mF	[T520D108M2R5AT	[T530Y108M2R5AT
1786918	[T495X108M004AT	E030]	E005]
1786963	E070]	1 mF	1 nF
1787205	1 mF	[T520X108M003AT	[C0402C102K1HACT
1787234	[T495E108M006AT	E015]	U]
1787289	E050]	1 mF	1 nF
1787331	1 mF	[T520X108M003AT	[C0402C102K3GACT
	[T495X108M004AT	E030]	U]
	1 mF	1 mF	1 nF
	[T510E108M004AT	[T520X108M2R5AT	[C0402C102K3HACT
	E010]	E010]	U]
	1 mF	1 mF	1 nF
	[T510E108M004AT	[T520Y108M2R5AT	[C0402C102K3RACT
	E018]	E010]	U]

Multisim 14.0 Power Pro Components

1 nF [C0402C102K4RACT U]	1 nF [C0603C102K4GACT U]	1 nF [C0805C102K3RACT U]	1 nF [C1206C102K4RACT U]
1 nF [C0402C102K5HACT U]	1 nF [C0603C102K4RACT U]	1 nF [C0805C102K4RACT U]	1 nF [C1206C102K5GACT U]
1 nF [C0402C102K5RACT U]	1 nF [C0603C102K5GACT U]	1 nF [C0805C102K5GACT U]	1 nF [C1206C102K5RACT U]
1 nF [C0402C102K8RACT U]	1 nF [C0603C102K5HACT U]	1 nF [C0805C102K5RACT U]	1 nF [C1206C102KCGAC TU]
1 nF [C0402C102K9RACT U]	1 nF [C0603C102K5RACT U]	1 nF [C0805C102K8RACT U]	1 nF [C1210C102K1GACT U]
1 nF [C0603C102K1HACT U]	1 nF [C0603C102K8RACT U]	1 nF [C0805C102KARACT U]	1 nF [C1210C102K2GACT U]
1 nF [C0603C102K1RACT U]	1 nF [C0603C102K9RACT U]	1 nF [C1206C102K1GACT U]	1 nF [C1210C102K5GACT U]
1 nF [C0603C102K2RACT U]	1 nF [C0805C102K1GACT U]	1 nF [C1206C102K1RACT U]	1 nF [C1210C102KBGAC TU]
1 nF [C0603C102K3GACT U]	1 nF [C0805C102K1RACT U]	1 nF [C1206C102K2GACT U]	1 nF [C1210C102KCGAC TU]
1 nF [C0603C102K3HACT U]	1 nF [C0805C102K2RACT U]	1 nF [C1206C102K2RACT U]	1 nF [C1210C102KDGAC TU]
1 nF [C0603C102K3RACT U]	1 nF [C0805C102K3GACT U]	1 nF [C1206C102K3RACT U]	1 nF [C1812C102K1GACT U]

Multisim 14.0 Power Pro Components

1 nF [C1812C102K2GACT U]	1 nF [CA064C102K8RACT U]	1 uF [C0805C105K4PACT U]	1 uF [C1206C105K3PACT U]
1 nF [C1812C102K5GACT U]	1 uF [C0402C105K8PACT U]	1 uF [C0805C105K4RACT U]	1 uF [C1206C105K3RACT U]
1 nF [C1812C102KBGAC TU]	1 uF [C0402C105K9PACT U]	1 uF [C0805C105K8NAC TU]	1 uF [C1206C105K4RACT U]
1 nF [C1812C102KCGAC TU]	1 uF [C0603C105K3PACT U]	1 uF [C0805C105K8PACT U]	1 uF [C1206C105K5RACT U]
1 nF [C1812C102KDGAC TU]	1 uF [C0603C105K4PACT U]	1 uF [C0805C105K8RACT U]	1 uF [C1206C105K8RACT U]
1 nF [C1825C102KBGAC TU]	1 uF [C0603C105K4RACT U]	1 uF [C0805C105K9PACT U]	1 uF [C1206C105K9RACT U]
1 nF [C2220C102KBGAC TU]	1 uF [C0603C105K8PACT U]	1 uF [C0805C105K9RACT U]	1 uF [C1206C105M3VAC TU]
1 nF [C2225C102KBGAC TU]	1 uF [C0603C105K8RACT U]	1 uF [C0805C105M3VAC TU]	1 uF [C1206C105M4VAC TU]
1 nF [CA064C102K3RACT U]	1 uF [C0603C105K9PACT U]	1 uF [C0805C105M4VAC TU]	1 uF [C1206C105M8VAC TU]
1 nF [CA064C102K4RACT U]	1 uF [C0603C105K9RACT U]	1 uF [C0805C105M8VAC TU]	1 uF [C1206F105K4RACT U]
1 nF [CA064C102K5RACT U]	1 uF [C0805C105K3PACT U]	1 uF [C1206C105K3NAC TU]	1 uF [C1210C105K1RACT U]

Multisim 14.0 Power Pro Components

1 uF [C1210C105K3PACT U]	1 uF [C1210C105M8VAC TU]	1 uF [C1825C105KARACT U]	1 uF [T491A105M016AT]
1 uF [C1210C105K3RACT U]	1 uF [C1210F105K3RACT U]	1 uF [C1825C105M5UAC TU]	1 uF [T491A105M020AT]
1 uF [C1210C105K4PACT U]	1 uF [C1210F105K4RACT U]	1 uF [C2220C105K5R1C7 186]	1 uF [T491A105M025AT]
1 uF [C1210C105K4RACT U]	1 uF [C1812C105K3RACT U]	1 uF [C2220C105K5RACT U]	1 uF [T491B105M025AT]
1 uF [C1210C105K5NAC TU]	1 uF [C1812C105K5RACT U]	1 uF [C2220C105KARACT U]	1 uF [T491B105M035AT]
1 uF [C1210C105K5PACT U]	1 uF [C1812C105M5UAC TU]	1 uF [C2225C105K1RACT U]	1 uF [T491B105M050AT]
1 uF [C1210C105K5RACT U]	1 uF [C1812F105K1RACT U]	1 uF [C2225C105K5RACT U]	1 uF [T491C105M050AT]
1 uF [C1210C105K8RACT U]	1 uF [C1812F105K3RACT U]	1 uF [C2225C105KARACT U]	1 uF [T491S105M020AT]
1 uF [C1210C105K9RACT U]	1 uF [C1812F105K5RACT U]	1 uF [C2225C105M5UAC TU]	1 uF [T491V105M050AT]
1 uF [C1210C105M3VAC TU]	1 uF [C1825C105K2RACT U]	1 uF [T409C105M025AH 4250]	1 uF [T491A105M016AT]
1 uF [C1210C105M5UAC TU]	1 uF [C1825C105K5RACT U]	1 uF [T489A105M025AT E6K6]	1 uF [T494A105M020AT]
			1 uF [T494A105M025AT]
			1 uF [T494A105M035AT]
			1 uF [T494B105M025AT]

Multisim 14.0 Power Pro Components

1 uF [T494B105M035AT]	1.1 nF [C0402C112K3HACT U]	1.2 nF [C0402C122K3HACT U]	1.2 nF [C0603C122K5RACT U]
1 uF [T494B105M050AT]	1.1 nF [C0402C112K5HACT U]	1.2 nF [C0402C122K3RACT U]	1.2 nF [C0805C122K1GACT U]
1 uF [T494C105M050AT]	1.1 nF [C0603C112K1HACT U]	1.2 nF [C0402C122K4RACT U]	1.2 nF [C0805C122K1RACT U]
1 uF [T494V105M050AT]	1.1 nF [C0603C112K3HACT U]	1.2 nF [C0402C122K5HACT U]	1.2 nF [C0805C122K2RACT U]
1 uF [T495A105M020AT E3K0]	1.1 nF [C0603C112K5HACT U]	1.2 nF [C0402C122K5RACT U]	1.2 nF [C0805C122K3GACT U]
1 uF [T495A105M035AT E3K0]	1.1 nF [C1210C112KBGAC TU]	1.2 nF [C0603C122K1HACT U]	1.2 nF [C0805C122K4RACT U]
1 uF [T495B105M035AT E1K7]	1.1 nF [C1812C112KBGAC TU]	1.2 nF [C0603C122K1RACT U]	1.2 nF [C0805C122K5GACT U]
1 uF [T497A105M015AT 6110]	1.1 nF [C1825C112KBGAC TU]	1.2 nF [C0603C122K3HACT U]	1.2 nF [C0805C122K5RACT U]
1 uF [T498A105M016AT E6K5]	1.1 nF [C2220C112KBGAC TU]	1.2 nF [C0603C122K3RACT U]	1.2 nF [C0805C122KARACT U]
1 uF [T498A105M020AT E5K9]	1.1 nF [C2225C112KBGAC TU]	1.2 nF [C0603C122K4RACT U]	1.2 nF [C1206C122K1GACT U]
1 uF [T498A105M035AT E10K]	1.1 nF [CDR33BP112BKSM]	1.2 nF [C0603C122K5HACT U]	1.2 nF [C1206C122K1RACT U]

Multisim 14.0 Power Pro Components

1.2 nF [C1206C122K2GACT U]	1.2 uF [C0805C125K8PACT U]	1.2 uF [C1825C125M5UAC TU]	1.3 nF [C2220C132KBGAC TU]
1.2 nF [C1206C122K2RACT U]	1.2 uF [C0805C125K8RACT U]	1.2 uF [C2220C125K5RACT U]	1.3 nF [C2225C132KBGAC TU]
1.2 nF [C1206C122K5GACT U]	1.2 uF [C0805C125K9PACT U]	1.2 uF [C2225C125KARACT U]	1.5 mF [T530X158M003AT E008]
1.2 nF [C1206C122K5RACT U]	1.2 uF [C0805C125K9RACT U]	1.3 nF [C0402C132K3HACT U]	1.5 mF [T530X158M2R5AT E005]
1.2 nF [C1210C122KBGAC TU]	1.2 uF [C1206C125K3RACT U]	1.3 nF [C0402C132K5HACT U]	1.5 nF [C0402C152K3HACT U]
1.2 nF [C1812C122KBGAC TU]	1.2 uF [C1206C125K4RACT U]	1.3 nF [C0603C132K1HACT U]	1.5 nF [C0402C152K3RACT U]
1.2 nF [C1825C122KBGAC TU]	1.2 uF [C1206C125K8RACT U]	1.3 nF [C0603C132K3HACT U]	1.5 nF [C0402C152K4RACT U]
1.2 nF [C2220C122KBGAC TU]	1.2 uF [C1210C125K3PACT U]	1.3 nF [C0603C132K5HACT U]	1.5 nF [C0402C152K5HACT U]
1.2 nF [C2225C122KBGAC TU]	1.2 uF [C1210C125K3RACT U]	1.3 nF [C1210C132KBGAC TU]	1.5 nF [C0402C152K5RACT U]
1.2 uF [C0805C125K4PACT U]	1.2 uF [C1210F125K4RACT U]	1.3 nF [C1812C132KBGAC TU]	1.5 nF [C0402C152K8RACT U]
1.2 uF [C0805C125K4RACT U]	1.2 uF [C1825C125K5RACT U]	1.3 nF [C1825C132KBGAC TU]	1.5 nF [C0603C152K1HACT U]

Multisim 14.0 Power Pro Components

1.5 nF [C0603C152K1RACT U]	1.5 nF [C0805C152K3RACT U]	1.5 nF [C1206C152K5RACT U]	1.5 uF [C0805C155K4RACT U]
1.5 nF [C0603C152K2RACT U]	1.5 nF [C0805C152K4GACT U]	1.5 nF [C1210C152K1GACT U]	1.5 uF [C0805C155K8PACT U]
1.5 nF [C0603C152K3HACT U]	1.5 nF [C0805C152K4RACT U]	1.5 nF [C1210C152K5GACT U]	1.5 uF [C0805C155K8RACT U]
1.5 nF [C0603C152K3RACT U]	1.5 nF [C0805C152K5GACT U]	1.5 nF [C1210C152KBGAC TU]	1.5 uF [C0805C155K9PACT U]
1.5 nF [C0603C152K4RACT U]	1.5 nF [C0805C152K5RACT U]	1.5 nF [C1812C152K2GACT U]	1.5 uF [C0805C155K9RACT U]
1.5 nF [C0603C152K5HACT U]	1.5 nF [C0805C152KARACT U]	1.5 nF [C1812C152KBGAC TU]	1.5 uF [C1206C155K3RACT U]
1.5 nF [C0603C152K5RACT U]	1.5 nF [C1206C152K1GACT U]	1.5 nF [C1825C152KBGAC TU]	1.5 uF [C1206C155K4PACT U]
1.5 nF [C0603C152K8RACT U]	1.5 nF [C1206C152K1RACT U]	1.5 nF [C2220C152KBGAC TU]	1.5 uF [C1206C155K4RACT U]
1.5 nF [C0805C152K1GACT U]	1.5 nF [C1206C152K2GACT U]	1.5 nF [C2225C152KBGAC TU]	1.5 uF [C1206C155K8PACT U]
1.5 nF [C0805C152K1RACT U]	1.5 nF [C1206C152K2RACT U]	1.5 nF [CDR04BP152BKSM]	1.5 uF [C1206C155K8RACT U]
1.5 nF [C0805C152K2RACT U]	1.5 nF [C1206C152K5GACT U]	1.5 uF [C0805C155K4PACT U]	1.5 uF [C1206C155K9RACT U]

Multisim 14.0 Power Pro Components

1.5 uF [C1210C155K3PACT U]	1.5 uF [T491A155M010AT]	1.5 uF [T494C155M035AT]	1.5KE47A-E3/54
1.5 uF [C1210C155K3RACT U]	1.5 uF [T491A155M016AT]	1.5 uF [T494C155M050AT]	1.5KE47AG
1.5 uF [C1210C155K4RACT U]	1.5 uF [T491A155M020AT]	1.5 uF [T494D155M050AT]	1.5KE47ARL4G
1.5 uF [C1210C155K4RACT U]	1.5 uF [T491A155M025AT]	1.5 uF [T494S155M020AT]	1.5KE51CA-E3/54
1.5 uF [C1210F155K4RACT U]	1.5 uF [T491B155M025AT]	1.5 uF [T498C155M035AT E3K3]	1.5KE75ARL4G
1.5 uF [C1825C155K5RACT U]	1.5 uF [T491B155M035AT]	1.5KE100A-E3/54	1.5KE91A-E3/54
1.5 uF [C1825C155M5UAC TU]	1.5 uF [T491C155M035AT]	1.5KE100CA-E3/54	1.5KE91ARL4G
1.5 uF [C2220C155K5RACT U]	1.5 uF [T491C155M050AT]	1.5KE110CA-E3/54	1.5SMC12AT3G
1.5 uF [C2225C155K5RACT U]	1.5 uF [T491D155M050AT]	1.5KE12A-E3/54	1.5SMC13A-E3/57T
1.5 uF [C2225C155K5RACT U]	1.5 uF [T491S155M020AT]	1.5KE12CA-E3/54	1.5SMC15AT3G
1.5 uF [C2225C155M5UAC TU]	1.5 uF [T494A155M010AT]	1.5KE130CA-E3/54	1.5SMC15CA- E3/57T
1.5 uF [T419A155M015AH 4250]	1.5 uF [T494A155M016AT]	1.5KE160CA-E3/54	1.5SMC180A- E3/57T
1.5 uF [T489C155M050AT E1K5]	1.5 uF [T494B155M025AT]	1.5KE180A-E3/54	1.5SMC18AT3G
	1.5 uF [T494B155M035AT]	1.5KE18A-E3/54	1.5SMC18CA- E3/57T
		1.5KE200A-E3/54	1.5SMC20AT3G
		1.5KE200CA-E3/54	1.5SMC24AT3G
		1.5KE20A-E3/51	1.5SMC33AT3G
		1.5KE36A-E3/54	1.5SMC39A-E3/57T
		1.5KE36CA-E3/54	1.5SMC39AT3G
		1.5KE39ARL4G	1.5SMC43AT3G
		1.5KE39CA-E3/54	1.5SMC540A- E3/57T
			1.5SMC6.8A/57T

Multisim 14.0 Power Pro Components

1.5SMC6.8AT3G	1.6 nF [C2220C162KBGAC TU]	1.8 nF [C0805C182K1RACT U]	1.8 nF [C1210C182K1GACT U]
1.5SMC6.8CA- E3/57T	1.6 nF [C2225C162KBGAC TU]	1.8 nF [C0805C182K2RACT U]	1.8 nF [C1210C182K2GACT U]
1.5SMC62AT3G	1.8 nF [C0402C182K3RACT U]	1.8 nF [C0805C182K4RACT U]	1.8 nF [C1210C182K5GACT U]
1.5SMC75CA- E3/57T	1.8 nF [C0402C182K5RACT U]	1.8 nF [C0805C182K5GACT U]	1.8 nF [C1210C182KBGAC TU]
1.5SMC91AT3G	1.8 nF [C0603C182K1HACT U]	1.8 nF [C0805C182K5RACT U]	1.8 nF [C1812C182KBGAC TU]
1.6 nF [C0603C162K1HACT U]	1.8 nF [C0603C182K1HACT U]	1.8 nF [C0805C182K5RACT U]	1.8 nF [C1812C182KBGAC TU]
1.6 nF [C0603C162K3HACT U]	1.8 nF [C0603C182K1RACT U]	1.8 nF [C0805C182KARACT U]	1.8 nF [C1825C182KBGAC TU]
1.6 nF [C0603C162K5HACT U]	1.8 nF [C0603C182K3HACT U]	1.8 nF [C1206C182K1GACT U]	1.8 nF [C2220C182KBGAC TU]
1.6 nF [C0805C162K4GACT U]	1.8 nF [C0603C182K3RACT U]	1.8 nF [C1206C182K1RACT U]	1.8 nF [C2225C182KBGAC TU]
1.6 nF [C1206C162K5GACT U]	1.8 nF [C0603C182K5HACT U]	1.8 nF [C1206C182K2GACT U]	1.8 uF [C0805C185K4PACT U]
1.6 nF [C1210C162KBGAC TU]	1.8 nF [C0603C182K5RACT U]	1.8 nF [C1206C182K5GACT U]	1.8 uF [C0805C185K4RACT U]
1.6 nF [C1812C162KBGAC TU]	1.8 nF [C0805C182K1GACT U]	1.8 nF [C1206C182K5RACT U]	1.8 uF [C0805C185K8PACT U]
1.6 nF [C1825C162KBGAC TU]			

Multisim 14.0 Power Pro Components

1.8 uF [C0805C185K8RACT U]	1.8 uF [C2225C185K5RACT U]	10 nF [C0603C103K2RACT U]	10 nF [C0805C103K3GACT U]
1.8 uF [C0805C185K9PACT U]	1.8 uF [C2225C185M5UAC TU]	10 nF [C0603C103K3GACT U]	10 nF [C0805C103K3HACT U]
1.8 uF [C0805C185K9RACT U]	1_AMP 10 nF [C0201C103K4PACT U]	10 nF [C0603C103K3HACT U]	10 nF [C0805C103K3RACT U]
1.8 uF [C1206C185K3PACT U]	10 nF [C0201C103K8PACT U]	10 nF [C0603C103K3RACT U]	10 nF [C0805C103K4RACT U]
1.8 uF [C1206C185K4RACT U]	10 nF [C0201C103K9PACT U]	10 nF [C0603C103K4RACT U]	10 nF [C0805C103K5GACT U]
1.8 uF [C1206C185K8RACT U]	10 nF [C0402C103K3RACT U]	10 nF [C0603C103K5RACT U]	10 nF [C0805C103K5HACT U]
1.8 uF [C1210C185K3PACT U]	10 nF [C0402C103K4RACT U]	10 nF [C0603C103K8RACT U]	10 nF [C0805C103K5RACT U]
1.8 uF [C1210C185K3RACT U]	10 nF [C0402C103K5RACT U]	10 nF [C0603C103K9RACT U]	10 nF [C0805C103K8RACT U]
1.8 uF [C1210F185K4RACT U]	10 nF [C0402C103K8RACT U]	10 nF [C0805C103K1GACT U]	10 nF [C0805C103KARACT U]
1.8 uF [C1825C185K5RACT U]	10 nF [C0402C103K9RACT U]	10 nF [C0805C103K1HACT U]	10 nF [C0805C103M1UAC TU]
1.8 uF [C2220C185K5RACT U]	10 nF [C0603C103K1RACT U]	10 nF [C0805C103K1RACT U]	10 nF [C0805C103M5UAC TU]

Multisim 14.0 Power Pro Components

10 nF [C0805F103K1RACT U]	10 nF [C1206C103K4GACT U]	10 nF [C1210C103KARACT U]	10 nF [C2225C103K2GACT U]
10 nF [C0805F103K2RACT U]	10 nF [C1206C103K4RACT U]	10 nF [C1812C103K1GACT U]	10 nF [C2225C103KCGAC TU]
10 nF [C0805F103K3RACT U]	10 nF [C1206C103K5HACT U]	10 nF [C1812C103K1RACT U]	10 nF [CA064C103K3RACT U]
10 nF [C0805F103K4RACT U]	10 nF [C1206C103K5RACT U]	10 nF [C1812C103K2RACT U]	10 nF [CA064C103K4RACT U]
10 nF [C0805F103K5RACT U]	10 nF [C1206C103KARACT U]	10 nF [C1812C103K5GACT U]	10 nF [CA064C103K5RACT U]
10 nF [C1206C103K1HACT U]	10 nF [C1206C103M1UAC TU]	10 nF [C1812C103K5RACT U]	10 nF [CA064C103K8RACT U]
10 nF [C1206C103K1RACT U]	10 nF [C1206C103M5UAC TU]	10 nF [C1825C103K1GACT U]	10 pF [C0402C100K3GACT U]
10 nF [C1206C103K2RACT U]	10 nF [C1210C103K1RACT U]	10 nF [C1825C103K2GACT U]	10 pF [C0402C100K4GACT U]
10 nF [C1206C103K3GACT U]	10 nF [C1210C103K2RACT U]	10 nF [C1825C103K5GACT U]	10 pF [C0402C100K5GACT U]
10 nF [C1206C103K3HACT U]	10 nF [C1210C103K5GACT U]	10 nF [C2220C103K1GACT U]	10 pF [C0402C100K8GACT U]
10 nF [C1206C103K3RACT U]	10 nF [C1210C103K5RACT U]	10 nF [C2220C103K2GACT U]	10 pF [C0603C100K1GACT U]

Multisim 14.0 Power Pro Components

10 pF [C0603C100K2GACT U]	10 pF [C1206C100K5GACT U]	10 pF [CA064C100K4GAC TU]	10 uF [C1206C106K8PACT U]
10 pF [C0603C100K3GACT U]	10 pF [C1206C100KBGAC TU]	10 pF [CA064C100K5GAC TU]	10 uF [C1206C106K8RACT U]
10 pF [C0603C100K5GACT U]	10 pF [C1210C100K2GACT U]	10 uF [A700V106M016AT E045]	10 uF [C1206C106K9PACT U]
10 pF [C0805C100K1GACT U]	10 pF [C1210C100K5GACT U]	10 uF [A700V106M12RAT E060]	10 uF [C1206C106K9RACT U]
10 pF [C0805C100K2GACT U]	10 pF [C1210C100KBGAC TU]	10 uF [C0805C106K4PACT U]	10 uF [C1206C106M8VAC TU]
10 pF [C0805C100K5GACT U]	10 pF [C1812C100KBGAC TU]	10 uF [C0805C106K8PACT U]	10 uF [C1206C106M9VAC TU]
10 pF [C0805C100KBGAC TU]	10 pF [C1825C100KBGAC TU]	10 uF [C0805C106K9PACT U]	10 uF [C1210C106K3PACT U]
10 pF [C0805C100KDGAC TU]	10 pF [C2220C100KBGAC TU]	10 uF [C0805C106M9VAC TU]	10 uF [C1210C106K3RACT U]
10 pF [C0805H100K5GAC TU]	10 pF [C2225C100KBGAC TU]	10 uF [C1206C106K3PACT U]	10 uF [C1210C106K4PACT U]
10 pF [C1206C100K1GACT U]	10 pF [CA064C100K1GAC TU]	10 uF [C1206C106K4PACT U]	10 uF [C1210C106K4RACT U]
10 pF [C1206C100K2GACT U]	10 pF [CA064C100K2GAC TU]	10 uF [C1206C106K4RACT U]	10 uF [C1210C106K8NAC TU]

Multisim 14.0 Power Pro Components

10 uF [C1210C106K8PACT U]	10 uF [T491A106M016AT]	10 uF [T491D106M050AT]	10 uF [T494A106M010AT]
10 uF [C1210C106K8RACT U]	10 uF [T491A106M020AT]	10 uF [T491S106M004AT]	10 uF [T494A106M016AT]
10 uF [C1210C106K9PACT U]	10 uF [T491B106M004AT]	10 uF [T491S106M006AT]	10 uF [T494A106M020AT]
10 uF [C1210C106K9RACT U]	10 uF [T491B106M010AT]	10 uF [T491S106M010AT]	10 uF [T494B106M004AT]
10 uF [C1210C106K9RACT U]	10 uF [T491B106M016AT]	10 uF [T491T106M006AT]	10 uF [T494B106M006AT]
10 uF [C1210C106M4VAC TU]	10 uF [T491B106M020AT]	10 uF [T491T106M010AT]	10 uF [T494B106M010AT]
10 uF [C1210C106M8VAC TU]	10 uF [T491C106M010AT]	10 uF [T491T106M016AT]	10 uF [T494B106M020AT]
10 uF [C1210C106M9VAC TU]	10 uF [T491C106M016AT]	10 uF [T491U106M016AT]	10 uF [T494C106M010AT]
10 uF [T429E106M020AH 4250]	10 uF [T491C106M020AT]	10 uF [T491U106M020AT]	10 uF [T494C106M016AT]
10 uF [T429H106M035AH 4250]	10 uF [T491C106M025AT]	10 uF [T491V106M035AT]	10 uF [T494C106M020AT]
10 uF [T491A106M004AT]	10 uF [T491C106M035AT]	10 uF [T491X106M050AT]	10 uF [T494C106M025AT]
10 uF [T491A106M006AT]	10 uF [T491D106M025AT]	10 uF [T493C106M020AH 6110]	10 uF [T494C106M035AT]
10 uF [T491A106M010AT]	10 uF [T491D106M035AT]	10 uF [T494A106M004AT]	10 uF [T494D106M025AT]
		10 uF [T494A106M006AT]	10 uF [T494D106M035AT]

Multisim 14.0 Power Pro Components

10 uF [T494D106M050AT]	10 uF [T495B106M020AT E1K0]	10 uF [T495X106M050AT E250]	10 uF [T498D106M035AT E700]
10 uF [T494S106M004AT]	10 uF [T495C106M020AT E400]	10 uF [T495X106M050AT E260]	10 uF [T498D106M050AT E1K0]
10 uF [T494S106M006AT]	10 uF [T495C106M020AT E475]	10 uF [T495X106M050AT E300]	10 uF [T510X106M050AT E090]
10 uF [T494S106M010AT]	10 uF [T495C106M025AT E275]	10 uF [T496D106M025AT 6110]	10 uF [T510X106M050AT E120]
10 uF [T494T106M006AT]	10 uF [T495C106M025AT E450]	10 uF [T497F106M015AT 6110]	10 uF [T520A106M010AT E080]
10 uF [T494T106M010AT]	10 uF [T495D106M035AT E125]	10 uF [T498B106M006AT E2K1]	10 uF [T520B106M016AT E100]
10 uF [T494U106M016AT]	10 uF [T495D106M035AT E250]	10 uF [T498B106M010AT E1K8]	10 uF [T521D106M050AT E090]
10 uF [T494U106M020AT]	10 uF [T495D106M035AT E300]	10 uF [T498B106M016AT E2K8]	10 uF [T521X106M063AT E050]
10 uF [T494V106M035AT]	10 uF [T495T106M016AT E4K0]	10 uF [T498C106M016AT E1K4]	10 uF [T541X106M063AH 6510]
10 uF [T494X106M050AT]	10 uF [T495X106M035AT E200]	10 uF [T498C106M020AT E1K1]	10_AMP
10 uF [T495A106M010AT E1K8]	10 uF [T495X106M035AT E250]	10 uF [T498C106M025AT E1K1]	100 nF [C0201C104K9PACT U]
10 uF [T495B106M010AT E750]			100 nF [C0402C104K4PACT U]

Multisim 14.0 Power Pro Components

100 nF [C0402C104K4RACT U]	100 nF [C0603C104M4VAC TU]	100 nF [C0805C104M5VAC TU]	100 nF [C1206F104K1RACT U]
100 nF [C0402C104K8PACT U]	100 nF [C0603C104M8VAC TU]	100 nF [C1206C104K1RACT U]	100 nF [C1206F104K2RACT U]
100 nF [C0402C104K8RACT U]	100 nF [C0805C104K1RACT U]	100 nF [C1206C104K2RACT U]	100 nF [C1206F104K3RACT U]
100 nF [C0402C104K9PACT U]	100 nF [C0805C104K3RACT U]	100 nF [C1206C104K3GACT U]	100 nF [C1206F104K4RACT U]
100 nF [C0402C104K9RACT U]	100 nF [C0805C104K4RACT U]	100 nF [C1206C104K3HACT U]	100 nF [C1206F104K5RACT U]
100 nF [C0603C104K3RACT U]	100 nF [C0805C104K5RACT U]	100 nF [C1206C104K3RACT U]	100 nF [C1210C104K1GACT U]
100 nF [C0603C104K4RACT U]	100 nF [C0805C104K8RACT U]	100 nF [C1206C104K4RACT U]	100 nF [C1210C104K1HACT U]
100 nF [C0603C104K5RACT U]	100 nF [C0805C104K9RACT U]	100 nF [C1206C104K5RACT U]	100 nF [C1210C104K1RACT U]
100 nF [C0603C104K8RACT U]	100 nF [C0805C104M3VAC TU]	100 nF [C1206C104KARACT U]	100 nF [C1210C104K2RACT U]
100 nF [C0603C104K9RACT U]	100 nF [C0805C104M4VAC TU]	100 nF [C1206C104M1UAC TU]	100 nF [C1210C104K3GACT U]
100 nF [C0603C104M3VAC TU]	100 nF [C0805C104M5UAC TU]	100 nF [C1206C104M5UAC TU]	100 nF [C1210C104K3HACT U]

Multisim 14.0 Power Pro Components

100 nF [C1210C104K3RACT U]	100 nF [C1210F104K3RACT U]	100 nF [C1812C104M1UAC TU]	100 nF [C2225C104K2RACT U]
100 nF [C1210C104K4RACT U]	100 nF [C1210F104K4RACT U]	100 nF [C1812F104K1RACT U]	100 nF [C2225C104K5RACT U]
100 nF [C1210C104K5GACT U]	100 nF [C1210F104K5RACT U]	100 nF [C1812F104K2RACT U]	100 nF [CA064C104K4RACT U]
100 nF [C1210C104K5HACT U]	100 nF [C1812C104K1GACT U]	100 nF [C1812F104K3RACT U]	100 nF [CA064C104K8RACT U]
100 nF [C1210C104K5RACT U]	100 nF [C1812C104K1HACT U]	100 nF [C1812F104K5RACT U]	100 nF [T491A104M035AT]
100 nF [C1210C104K8RACT U]	100 nF [C1812C104K1R1C7 186]	100 nF [C1825C104K1RACT U]	100 nF [T491A104M050AT]
100 nF [C1210C104KARACT U]	100 nF [C1812C104K1RACT U]	100 nF [C1825C104K2RACT U]	100 nF [T494A104M035AT]
100 nF [C1210C104M1UAC TU]	100 nF [C1812C104K2RACT U]	100 nF [C2220C104K1GACT U]	100 pF [03028BR101AKZC]
100 nF [C1210C104M5UAC TU]	100 nF [C1812C104K5GACT U]	100 nF [C2220C104K2GACT U]	100 pF [C0201C101K3GACT U]
100 nF [C1210F104K1RACT U]	100 nF [C1812C104K5HACT U]	100 nF [C2220C104K5GACT U]	100 pF [C0402C101K1HACT U]
100 nF [C1210F104K2RACT U]	100 nF [C1812C104K5RACT U]	100 nF [C2225C104K1RACT U]	100 pF [C0402C101K3GACT U]

Multisim 14.0 Power Pro Components

100 pF [C0402C101K3HACT U]	100 pF [C0805C101K1GACT U]	100 pF [C1206C101K3GACT U]	100 pF [C1812C101KDGAC TU]
100 pF [C0402C101K4GACT U]	100 pF [C0805C101K2GACT U]	100 pF [C1206C101K5GACT U]	100 pF [C1812C101KHGAC TU]
100 pF [C0402C101K5GACT U]	100 pF [C0805C101K3GACT U]	100 pF [C1206C101KBGAC TU]	100 pF [C1825C101KBGAC TU]
100 pF [C0402C101K5HACT U]	100 pF [C0805C101K4GACT U]	100 pF [C1206C101KCGAC TU]	100 pF [C2220C101KBGAC TU]
100 pF [C0402C101K8GACT U]	100 pF [C0805C101K5GACT U]	100 pF [C1206C101KDGAC TU]	100 pF [C2225C101KBGAC TU]
100 pF [C0603C101K1GACT U]	100 pF [C0805C101KBGAC TU]	100 pF [C1206C101KGGAC TU]	100 pF [CA064C101K1GAC TU]
100 pF [C0603C101K3GACT U]	100 pF [C0805C101KCGAC TU]	100 pF [C1210C101K5GACT U]	100 pF [CA064C101K3GAC TU]
100 pF [C0603C101K4GACT U]	100 pF [C0805C101KDGAC TU]	100 pF [C1210C101KBGAC TU]	100 pF [CA064C101K5GAC TU]
100 pF [C0603C101K5GACT U]	100 pF [C0805H101K5GAC TU]	100 pF [C1210C101KCGAC TU]	100 pF [CA064C101K8GAC TU]
100 pF [C0603C101K5RACT U]	100 pF [C1206C101K1GACT U]	100 pF [C1210C101KDGAC TU]	100 uF [A700D107M006AT E015]
100 pF [C0603C101K8GACT U]	100 pF [C1206C101K2GACT U]	100 pF [C1812C101KBGAC TU]	100 uF [A700D107M006AT E018]

Multisim 14.0 Power Pro Components

100 uF [A700V107M002AT E018]	100 uF [T491B107M006AT]	100 uF [T491U107M004AT]	100 uF [T494D107M004AT]
100 uF [A700V107M002AT E025]	100 uF [T491B107M010AT] 100 uF [T491C107M004AT]	100 uF [T491U107M006AT]	100 uF [T494D107M006AT]
100 uF [A700V107M002AT E028]	100 uF [T491C107M006AT]	100 uF [T491V107M006AT]	100 uF [T494D107M010AT]
100 uF [A700X107M008AT E010]	100 uF [T491C107M010AT] 100 uF [T491D107M004AT]	100 uF [T491V107M010AT] 100 uF [T491V107M016AT]	100 uF [T494D107M016AT]
100 uF [A700X107M008AT E015]	100 uF [T491D107M006AT]	100 uF [T491X107M016AT]	100 uF [T494E107M020AT]
100 uF [A700X107M010AT E010]	100 uF [T491D107M010AT]	100 uF [T491X107M020AT]	100 uF [T494T107M004AT]
100 uF [A700X107M010AT E015]	100 uF [T491D107M016AT]	100 uF [T491X107M025AT]	100 uF [T494T107M2R5AT]
100 uF [T489C107M010AT E500]	100 uF [T491D107M020AT]	100 uF [T494A107M004AT] 100 uF [T494B107M004AT]	100 uF [T494U107M004AT] 100 uF [T494U107M006AT]
100 uF [T489D107M010AT E150]	100 uF [T491E107M020AT]	100 uF [T494B107M006AT]	100 uF [T494V107M006AT]
100 uF [T489D107M010AT E440]	100 uF [T491T107M004AT]	100 uF [T494C107M004AT] 100 uF [T494C107M006AT]	100 uF [T494V107M010AT]
100 uF [T491A107M004AT]	100 uF [T491T107M2R5AT]	100 uF [T494C107M010AT]	100 uF [T494V107M016AT]
100 uF [T491B107M004AT]			100 uF [T494X107M016AT]

Multisim 14.0 Power Pro Components

100 uF [T494X107M020AT]	100 uF [T495D107M016AT E100]	100 uF [T495X107M020AT E100]	100 uF [T520B107M003AT E035]
100 uF [T494X107M025AT]	100 uF [T495D107M016AT E125]	100 uF [T495X107M020AT E150]	100 uF [T520B107M003AT E040]
100 uF [T495B107M006AT E400]	100 uF [T495E107M020AT E060]	100 uF [T498D107M006AT E600]	100 uF [T520B107M003AT E070]
100 uF [T495B107M006AT E700]	100 uF [T495E107M020AT E200]	100 uF [T498D107M010AT E600]	100 uF [T520B107M004AT E035]
100 uF [T495B107M010AT E350]	100 uF [T495T107M2R5AT E3K0]	100 uF [T510E107M025AT E050]	100 uF [T520B107M004AT E040]
100 uF [T495C107M006AT E150]	100 uF [T495V107M006AT E150]	100 uF [T510X107M020AT E040]	100 uF [T520B107M004AT E070]
100 uF [T495D107M006AT E050]	100 uF [T495V107M010AT E100]	100 uF [T510X107M020AT E045]	100 uF [T520B107M006AT E015]
100 uF [T495D107M006AT E130]	100 uF [T495V107M010AT E150]	100 uF [T513D107M016AH 6110]	100 uF [T520B107M006AT E018]
100 uF [T495D107M010AT E050]	100 uF [T495X107M010AT E100]	100 uF [T513E107M025AH 6110]	100 uF [T520B107M006AT E025]
100 uF [T495D107M010AT E065]	100 uF [T495X107M016AT E080]	100 uF [T513X107M020AH 6110]	100 uF [T520B107M006AT E035]
100 uF [T495D107M010AT E080]	100 uF [T495X107M016AT E100]	100 uF [T513X107M020AH 6120]	100 uF [T520B107M006AT E040]

Multisim 14.0 Power Pro Components

100 uF [T520B107M006AT E070]	100 uF [T520T107M004AT E070]	100 uF [T520V107M010AT E025]	100 uF [T525D107M010AT E055]
100 uF [T520B107M2R5AT E035]	100 uF [T520T107M004AT E150]	100 uF [T520V107M010AT E045]	100 uF [T525T107M2R5AT E080]
100 uF [T520B107M2R5AT E040]	100 uF [T520T107M006AT E070]	100 uF [T520V107M010AT E050]	100 uF [T528I107M003ATE 200]
100 uF [T520C107M006AT E025]	100 uF [T520T107M2R5AT E070]	100 uF [T520W107M006AT E040]	100 uF [T540B107M004AH 6510]
100 uF [T520C107M006AT E045]	100 uF [T520U107M004AT E055]	100 uF [T520W107M010AT E040]	100 uF [T540D107M010AH 6510]
100 uF [T520C107M010AT E025]	100 uF [T520U107M006AT E055]	100 uF [T521D107M016AT E050]	10029449-001RLF 100V_100W
100 uF [T520C107M010AT E045]	100 uF [T520V107M006AT E007]	100 uF [T521V107M016AT E050]	10104111-0001LF 105081-0001
100 uF [T520D107M006AT E007]	100 uF [T520V107M006AT E009]	100 uF [T521X107M025AT E060]	10BQ015 10BQ040
100 uF [T520D107M010AT E018]	100 uF [T520V107M006AT E012]	100 uF [T525B107M003AT E080]	10Line_Bussed 10Line_Isolated
100 uF [T520D107M010AT E055]	100 uF [T520V107M006AT E045]	100 uF [T525B107M004AT E080]	10TQ045 10YQ045 10YQ045C
100 uF [T520D107M010AT E080]	100 uF [T520V107M010AT E018]	100 uF [T525D107M010AT E025]	11 pF [C0805C110KBGAC TU]

Multisim 14.0 Power Pro Components

11 pF [C1206C110KBGAC TU]	110 pF [C1206C111K5GACT U]	12 nF [C0402C123K9PACT U]	12 nF [C0805C123K4RACT U]
11 pF [C1210C110KBGAC TU]	110 pF [C1206C111KBGAC TU]	12 nF [C0402C123K9RACT U]	12 nF [C0805C123K5GACT U]
11 pF [C1812C110KBGAC TU]	110 pF [C1210C111KBGAC TU]	12 nF [C0603C123K1RACT U]	12 nF [C0805C123K5HACT U]
11 pF [C1825C110KBGAC TU]	110 pF [C1812C111KBGAC TU]	12 nF [C0603C123K3RACT U]	12 nF [C0805C123K5RACT U]
11 pF [C2220C110KBGAC TU]	110 pF [C1825C111KBGAC TU]	12 nF [C0603C123K4RACT U]	12 nF [C0805C123K8RACT U]
11 pF [C2225C110KBGAC TU]	110 pF [C2220C111KBGAC TU]	12 nF [C0603C123K5RACT U]	12 nF [C0805C123KARACT U]
110 pF [C0402C111K1HACT U]	110 pF [C2225C111KBGAC TU]	12 nF [C0805C123K1GACT U]	12 nF [C0805F123K1RACT U]
110 pF [C0402C111K3HACT U]	12 nF [C0402C123K4RACT U]	12 nF [C0805C123K1HACT U]	12 nF [C0805F123K3RACT U]
110 pF [C0402C111K5HACT U]	12 nF [C0402C123K5RACT U]	12 nF [C0805C123K1RACT U]	12 nF [C0805F123K4RACT U]
110 pF [C0603C111K5GACT U]	12 nF [C0402C123K8PACT U]	12 nF [C0805C123K3HACT U]	12 nF [C0805F123K5RACT U]
110 pF [C0805C111K1GACT U]	12 nF [C0402C123K8RACT U]	12 nF [C0805C123K3RACT U]	12 nF [C1206C123K1HACT U]

Multisim 14.0 Power Pro Components

12 nF [C1206C123K1RACT U]	12 nF [C1210C123K5HACT U]	12 pF [C0603C120K5GACT U]	12 pF [C2225C120KBGAC TU]
12 nF [C1206C123K2RACT U]	12 nF [C1210C123K5RACT U]	12 pF [C0805C120K1GACT U]	12 pF [CA064C120K5GAC TU]
12 nF [C1206C123K3HACT U]	12 nF [C1210C123KARACT U]	12 pF [C0805C120K5GACT U]	12 uF [C1210C126K8PACT U]
12 nF [C1206C123K5HACT U]	12 nF [C1812C123K1RACT U]	12 pF [C0805C120KBGAC TU]	120 nF [C0603C124K4RACT U]
12 nF [C1206C123K5RACT U]	12 nF [C2220C123K2GACT U]	12 pF [C1206C120K1GACT U]	120 nF [C0603C124K8RACT U]
12 nF [C1206C123KARACT U]	12 pF [C0201C120K3GACT U]	12 pF [C1206C120K5GACT U]	120 nF [C0805C124K1RACT U]
12 nF [C1210C123K1GACT U]	12 pF [C0402C120K4GACT U]	12 pF [C1206C120KBGAC TU]	120 nF [C0805C124K3RACT U]
12 nF [C1210C123K1HACT U]	12 pF [C0402C120K5GACT U]	12 pF [C1210C120KBGAC TU]	120 nF [C0805C124K4RACT U]
12 nF [C1210C123K3HACT U]	12 pF [C0603C120K1GACT U]	12 pF [C1812C120KBGAC TU]	120 nF [C0805C124K5RACT U]
12 nF [C1210C123K4RACT U]	12 pF [C0603C120K2GACT U]	12 pF [C1825C120KBGAC TU]	120 nF [C0805C124K8RACT U]
12 nF [C1210C123K5GACT U]	12 pF [C0603C120K3GACT U]	12 pF [C2220C120KBGAC TU]	120 nF [C1206C124K1RACT U]

Multisim 14.0 Power Pro Components

120 nF [C1206C124K2RACT U]	120 nF [C1210F124K4RACT U]	120 nF [C1812F124K3RACT U]	120 pF [C0603C121K5GACT U]
120 nF [C1206C124K3RACT U]	120 nF [C1210F124K5RACT U]	120 nF [C1812F124K5RACT U]	120 pF [C0805C121K1GACT U]
120 nF [C1206C124K4RACT U]	120 nF [C1812C124K1GACT U]	120 nF [C2220C124K1GACT U]	120 pF [C0805C121K2GACT U]
120 nF [C1206C124K5RACT U]	120 nF [C1812C124K1HACT U]	120 nF [C2220C124K5GACT U]	120 pF [C0805C121K5GACT U]
120 nF [C1206C124M5UAC TU]	120 nF [C1812C124K2RACT U]	120 nF [C2225C124K1RACT U]	120 pF [C1206C121K1GACT U]
120 nF [C1210C124K1RACT U]	120 nF [C1812C124K5GACT U]	120 pF [03029BR121AKZC] U]	120 pF [C1206C121K2GACT U]
120 nF [C1210C124K3HACT U]	120 nF [C1812C124K5HACT U]	120 pF [C0402C121K1HACT U]	120 pF [C1206C121K5GACT U]
120 nF [C1210C124K5HACT U]	120 nF [C1812C124K5RACT U]	120 pF [C0402C121K3HACT U]	120 pF [C1206C121KBGAC TU]
120 nF [C1210C124K5RACT U]	120 nF [C1812C124M1UAC TU]	120 pF [C0402C121K5GACT U]	120 pF [C1206C121KDGAC TU]
120 nF [C1210F124K1RACT U]	120 nF [C1812F124K1RACT U]	120 pF [C0402C121K5HACT U]	120 pF [C1210C121KBGAC TU]
120 nF [C1210F124K3RACT U]	120 nF [C1812F124K2RACT U]	120 pF [C0603C121K1GACT U]	120 pF [C1812C121KBGAC TU]

Multisim 14.0 Power Pro Components

120 pF [C1825C121KBGAC TU]	120 uF [A700X127M010AT E015]	13 pF [C0805C130K5GACT U]	130 pF [C0805H131K3GAC TU]
120 pF [C2220C121KBGAC TU]	120 uF [T520B127M006AT E035]	13 pF [C0805C130KBGAC TU]	130 pF [C1206C131KBGAC TU]
120 pF [C2225C121KBGAC TU]	120LQ045 120LQ100	13 pF [C1206C130KBGAC TU]	130 pF [C1210C131KBGAC TU]
120 pF [CA064C121K5GAC TU]	120V_100W 120V_250W	13 pF [C1210C130KBGAC TU]	130 pF [C1812C131KBGAC TU]
120 uF [A700D127M004AT E015]	1-282834-0 12A02CH-TL-E 12A02MH-TL-E	13 pF [C1812C130KBGAC TU]	130 pF [C1825C131KBGAC TU]
120 uF [A700D127M004AT E018]	12AU7A 12AX7A	13 pF [C1825C130KBGAC TU]	130 pF [C2220C131KBGAC TU]
120 uF [A700D127M006AT E012]	12BH7A 12CGQ150	13 pF [C2220C130KBGAC TU]	130 pF [C2225C131KBGAC TU]
120 uF [A700D127M006AT E015]	12CTQ045 12TQ045	13 pF [C2225C130KBGAC TU]	15 nF [C0402C153K4RACT U]
120 uF [A700D127M006AT E018]	12V_10W 12V_25W	130 pF [C0402C131K1HACT U]	15 nF [C0402C153K5RACT U]
120 uF [A700V127M002AT E018]	13 pF [C0603C130K2GACT U]	130 pF [C0402C131K3HACT U]	15 nF [C0402C153K8PACT U]
120 uF [A700X127M010AT E010]	13 pF [C0603C130K5GACT U]	130 pF [C0402C131K5HACT U]	15 nF [C0402C153K8RACT U]

Multisim 14.0 Power Pro Components

15 nF [C0402C153K9PACT U]	15 nF [C0805C153K4RACT U]	15 nF [C1206C153K1HACT U]	15 nF [C1210C153K1RACT U]
15 nF [C0402C153K9RACT U]	15 nF [C0805C153K5GACT U]	15 nF [C1206C153K1RACT U]	15 nF [C1210C153K2RACT U]
15 nF [C0603C153K1RACT U]	15 nF [C0805C153K5HACT U]	15 nF [C1206C153K2RACT U]	15 nF [C1210C153K3HACT U]
15 nF [C0603C153K3RACT U]	15 nF [C0805C153K5RACT U]	15 nF [C1206C153K3HACT U]	15 nF [C1210C153K5HACT U]
15 nF [C0603C153K4RACT U]	15 nF [C0805C153K8RACT U]	15 nF [C1206C153K4RACT U]	15 nF [C1210C153K5RACT U]
15 nF [C0603C153K5RACT U]	15 nF [C0805C153KARACT U]	15 nF [C1206C153K5HACT U]	15 nF [C1210C153KARACT U]
15 nF [C0805C153K1GACT U]	15 nF [C0805C153M5UAC TU]	15 nF [C1206C153K5RACT U]	15 nF [C1812C153K1GACT U]
15 nF [C0805C153K1HACT U]	15 nF [C0805F153K1RACT U]	15 nF [C1206C153KARACT U]	15 nF [C1812C153K1HACT U]
15 nF [C0805C153K1RACT U]	15 nF [C0805F153K3RACT U]	15 nF [C1206C153M5UAC TU]	15 nF [C1812C153K1RACT U]
15 nF [C0805C153K3HACT U]	15 nF [C0805F153K4RACT U]	15 nF [C1210C153K1GACT U]	15 nF [C1812C153K2RACT U]
15 nF [C0805C153K3RACT U]	15 nF [C0805F153K5RACT U]	15 nF [C1210C153K1HACT U]	15 nF [C1812C153K5GACT U]

Multisim 14.0 Power Pro Components

15 nF [C1812C153K5HACT U]	15 pF [C0603C150K1GACT U]	15 pF [C1206C150K2GACT U]	15 uF [A700V156M12RAT E040]
15 nF [C1812C153K5RACT U]	15 pF [C0603C150K2GACT U]	15 pF [C1206C150K5GACT U]	15 uF [C1210C156K4PACT U]
15 nF [C1825C153K5GACT U]	15 pF [C0603C150K4GACT U]	15 pF [C1206C150KBGAC TU]	15 uF [C1210C156K8PACT U]
15 nF [C2220C153K2GACT U]	15 pF [C0603C150K5GACT U]	15 pF [C1206C150KGGAC TU]	15 uF [C1210C156K9PACT U]
15 nF [C2225C153K5GACT U]	15 pF [C0805C150K1GACT U]	15 pF [C1210C150KBGAC TU]	15 uF [T409E156M004AH 4250]
15 nF [CA064C153K5RACT U]	15 pF [C0805C150K2GACT U]	15 pF [C1812C150KBGAC TU]	15 uF [T409H156M025AH 4250]
15 pF [C0201C150K3GACT U]	15 pF [C0805C150K3GACT U]	15 pF [C1825C150KBGAC TU]	15 uF [T419B156M004AH 4250]
15 pF [C0402C150K3GACT U]	15 pF [C0805C150K4GACT U]	15 pF [C2220C150KBGAC TU]	15 uF [T419D156M010AH 4250]
15 pF [C0402C150K4GACT U]	15 pF [C0805C150K5GACT U]	15 pF [C2225C150KBGAC TU]	15 uF [T429B156M004AH 4250]
15 pF [C0402C150K5GACT U]	15 pF [C0805C150KBGAC TU]	15 pF [CA064C150K4GAC TU]	15 uF [T429F156M010AH 4250]
15 pF [C0402C150K8GACT U]	15 pF [C1206C150K1GACT U]	15 pF [CA064C150K5GAC TU]	15 uF [T429F156M020AH 4250]

Multisim 14.0 Power Pro Components

15 uF [T489D156M025AT E300]	15 uF [T491D156M025AT]	15 uF [T494B156M004AT]	15 uF [T494S156M006AT]
15 uF [T491A156M004AT]	15 uF [T491D156M035AT]	15 uF [T494B156M006AT]	15 uF [T494T156M004AT]
15 uF [T491A156M006AT]	15 uF [T491S156M004AT]	15 uF [T494B156M010AT]	15 uF [T494T156M006AT]
15 uF [T491A156M010AT]	15 uF [T491S156M006AT]	15 uF [T494B156M016AT]	15 uF [T494T156M010AT]
15 uF [T491B156M004AT]	15 uF [T491T156M004AT]	15 uF [T494C156M006AT]	15 uF [T494U156M010AT]
15 uF [T491B156M006AT]	15 uF [T491T156M006AT]	15 uF [T494C156M010AT]	15 uF [T494U156M016AT]
15 uF [T491B156M010AT]	15 uF [T491T156M010AT]	15 uF [T494C156M016AT]	15 uF [T494X156M035AT]
15 uF [T491B156M016AT]	15 uF [T491U156M010AT]	15 uF [T494C156M020AT]	15 uF [T494X156M050AT]
15 uF [T491B156M025AT]	15 uF [T491U156M016AT]	15 uF [T494C156M025AT]	15 uF [T495B156M010AT E500]
15 uF [T491C156M006AT]	15 uF [T491X156M035AT]	15 uF [T494D156M020AT]	15 uF [T495C156M010AT E375]
15 uF [T491C156M016AT]	15 uF [T491X156M050AT]	15 uF [T494D156M025AT]	15 uF [T495C156M010AT E400]
15 uF [T491C156M025AT]	15 uF [T494A156M004AT]	15 uF [T494D156M035AT]	15 uF [T495D156M020AT E275]
15 uF [T491D156M020AT]	15 uF [T494A156M006AT]	15 uF [T494S156M004AT]	15 uF [T495D156M025AT E100]
	15 uF [T494A156M010AT]		

Multisim 14.0 Power Pro Components

15 uF [T495D156M025AT E275]	15 uF [T498C156M016AT E1K1]	15 uF [T521B156M016AT E090]	150 nF [C0603C154M3VAC TU]
15 uF [T495D156M035AT E225]	15 uF [T498D156M025AT E700]	15 uF [T521V156M025AT E090]	150 nF [C0603C154M4VAC TU]
15 uF [T495D156M035AT E300]	15 uF [T499B156M006AT E3K5]	15 uF [T521V156M035AT E100]	150 nF [C0603C154M8VAC TU]
15 uF [T495X156M025AT E200]	15 uF [T499D156M020AT E1K0]	15 uF [T521V156M035AT E125]	150 nF [C0805C154K3RACT U]
15 uF [T495X156M035AT E200]	15 uF [T513D156M035AH 6110]	15 uF [T521X156M063AT E035]	150 nF [C0805C154K4RACT U]
15 uF [T495X156M050AT E200]	15 uF [T520A156M010AT E080]	15 uF [T521X156M063AT E150]	150 nF [C0805C154K5RACT U]
15 uF [T495X156M050AT E300]	15 uF [T520D156M025AT E060]	15 uF [T541X156M063AH 6510]	150 nF [C0805C154K8RACT U]
15 uF [T497E156M010AT 6110]	15 uF [T520D156M025AT E080]	15 uF [T543T156M006AT E100]	150 nF [C0805C154M3VAC TU]
15 uF [T498B156M006AT E1K8]	15 uF [T520T156M004AT E100]	15_AMP	150 nF [C1206C154K1RACT U]
15 uF [T498B156M010AT E1K5]	15 uF [T520T156M006AT E100]	150 nF [C0603C154K4RACT U]	150 nF [C1206C154K2RACT U]
15 uF [T498C156M010AT E1K8]	15 uF [T520T156M12RAT E080]	150 nF [C0603C154K5RACT U]	150 nF [C1206C154K3RACT U]
		150 nF [C0603C154K8RACT U]	

Multisim 14.0 Power Pro Components

150 nF [C1206C154K4RACT U]	150 nF [C1210F154K1RACT U]	150 nF [C1812C154M1UAC TU]	150 nF [C2225C154K2RACT U]
150 nF [C1206C154K5RACT U]	150 nF [C1210F154K3RACT U]	150 nF [C1812C154M5UAC TU]	150 nF [T429A154M050AH 4250]
150 nF [C1206C154M5UAC TU]	150 nF [C1210F154K4RACT U]	150 nF [C1812F154K1RACT U]	150 nF [T491A154M035AT]
150 nF [C1206F154K1RACT U]	150 nF [C1210F154K5RACT U]	150 nF [C1812F154K2RACT U]	150 nF [T491A154M050AT]
150 nF [C1206F154K3RACT U]	150 nF [C1812C154K1GACT U]	150 nF [C1812F154K3RACT U]	150 nF [T491B154M050AT]
150 nF [C1206F154K4RACT U]	150 nF [C1812C154K1HACT U]	150 nF [C1812F154K5RACT U]	150 nF [T494A154M050AT]
150 nF [C1206F154K5RACT U]	150 nF [C1812C154K1RACT U]	150 nF [C1825C154K1RACT U]	150 nF [T494B154M050AT]
150 nF [C1210C154K1RACT U]	150 nF [C1812C154K2RACT U]	150 nF [C1825C154K5RACT U]	150 pF [C0402C151K1HACT U]
150 nF [C1210C154K3HACT U]	150 nF [C1812C154K5GACT U]	150 nF [C2220C154K1GACT U]	150 pF [C0402C151K3HACT U]
150 nF [C1210C154K5HACT U]	150 nF [C1812C154K5HACT U]	150 nF [C2220C154K5GACT U]	150 pF [C0402C151K3RACT U]
150 nF [C1210C154K5RACT U]	150 nF [C1812C154K5RACT U]	150 nF [C2225C154K1RACT U]	150 pF [C0402C151K4RACT U]
			150 pF [C0402C151K5GACT U]

Multisim 14.0 Power Pro Components

150 pF [C0402C151K5HACT U]	150 pF [C0805C151K5GACT U]	150 pF [CA064C151K5GAC TU]	150 uF [A700X157M010AT E010]
150 pF [C0402C151K5RACT U]	150 pF [C1206C151K1GACT U]	150 uF [A700D157M004AT E015]	150 uF [A700X157M010AT E015]
150 pF [C0402C151K8RACT U]	150 pF [C1206C151K2GACT U]	150 uF [A700D157M004AT E018]	150 uF [T429G157M006AH 4250]
150 pF [C0603C151K1GACT U]	150 pF [C1206C151K5GACT U]	150 uF [A700D157M2R5AT E015]	150 uF [T429X157M010AH 4250]
150 pF [C0603C151K3GACT U]	150 pF [C1206C151KBGAC TU]	150 uF [A700D157M2R5AT E018]	150 uF [T491B157M004AT]
150 pF [C0603C151K4GACT U]	150 pF [C1210C151KBGAC TU]	150 uF [A700V157M002AT E009]	150 uF [T491C157M004AT]
150 pF [C0603C151K5GACT U]	150 pF [C1812C151KBGAC TU]	150 uF [A700V157M002AT E018]	150 uF [T491C157M010AT]
150 pF [C0805C151K1GACT U]	150 pF [C1825C151KBGAC TU]	150 uF [A700V157M002AT E025]	150 uF [T491D157M004AT]
150 pF [C0805C151K2GACT U]	150 pF [C2220C151KBGAC TU]	150 uF [A700V157M002AT E028]	150 uF [T491D157M006AT]
150 pF [C0805C151K3GACT U]	150 pF [C2225C151KBGAC TU]	150 uF [A700X157M006AT E010]	150 uF [T491D157M010AT]
150 pF [C0805C151K4GACT U]	150 pF [CA064C151K4GAC TU]	150 uF [A700X157M006AT E015]	150 uF [T491D157M016AT]

Multisim 14.0 Power Pro Components

150 uF [T491V157M004AT]	150 uF [T494V157M004AT]	150 uF [T495D157M016AT E060]	150 uF [T510X157M016AT E040]
150 uF [T491V157M006AT]	150 uF [T494V157M006AT]	150 uF [T495D157M016AT E085]	150 uF [T513X157M016AH 6110]
150 uF [T491V157M010AT]	150 uF [T494V157M010AT]	150 uF [T495D157M016AT E100]	150 uF [T513X157M016AH 6120]
150 uF [T491X157M010AT]	150 uF [T494X157M010AT]	150 uF [T495D157M016AT E125]	150 uF [T520B157M003AT E025]
150 uF [T491X157M016AT]	150 uF [T494X157M016AT]	150 uF [T495D157M016AT E150]	150 uF [T520B157M003AT E035]
150 uF [T491X157M020AT]	150 uF [T494X157M020AT]	150 uF [T495V157M010AT E150]	150 uF [T520B157M003AT E040]
150 uF [T494B157M004AT]	150 uF [T495B157M004AT E900]	150 uF [T495X157M010AT E085]	150 uF [T520B157M003AT E070]
150 uF [T494C157M004AT]	150 uF [T495C157M006AT E200]	150 uF [T495X157M010AT E100]	150 uF [T520B157M004AT E015]
150 uF [T494C157M006AT]	150 uF [T495D157M006AT E050]	150 uF [T495X157M016AT E075]	150 uF [T520B157M004AT E018]
150 uF [T494C157M010AT]	150 uF [T495D157M006AT E125]	150 uF [T495X157M016AT E100]	150 uF [T520B157M004AT E025]
150 uF [T494D157M004AT]	150 uF [T495D157M010AT E050]	150 uF [T510X157M016AT E030]	150 uF [T520B157M004AT E030]
150 uF [T494D157M006AT]	150 uF [T495D157M010AT E060]		
150 uF [T494D157M010AT]	150 uF [T495D157M010AT E100]		

Multisim 14.0 Power Pro Components

150 uF [T520B157M004AT E035]	150 uF [T520C157M006AT E025]	150 uF [T520D157M008AT E040]	150 uF [T520U157M2R5AT E055]
150 uF [T520B157M004AT E040]	150 uF [T520C157M006AT E045]	150 uF [T520D157M008AT E055]	150 uF [T520V157M004AT E007]
150 uF [T520B157M004AT E070]	150 uF [T520C157M006AT E055]	150 uF [T520D157M010AT E025]	150 uF [T520V157M004AT E009]
150 uF [T520B157M006AT E035]	150 uF [T520C157M010AT E055]	150 uF [T520D157M010AT E040]	150 uF [T520V157M004AT E012]
150 uF [T520B157M006AT E045]	150 uF [T520D157M004AT E007]	150 uF [T520D157M010AT E055]	150 uF [T520V157M004AT E015]
150 uF [T520B157M006AT E070]	150 uF [T520D157M006AT E006]	150 uF [T520L157M006AT E012]	150 uF [T520V157M004AT E025]
150 uF [T520C157M004AT E015]	150 uF [T520D157M006AT E007]	150 uF [T520L157M006AT E025]	150 uF [T520V157M006AT E006]
150 uF [T520C157M004AT E025]	150 uF [T520D157M006AT E015]	150 uF [T520M157M006AT E070]	150 uF [T520V157M006AT E007]
150 uF [T520C157M004AT E045]	150 uF [T520D157M006AT E025]	150 uF [T520U157M004AT E055]	150 uF [T520V157M006AT E009]
150 uF [T520C157M004AT E100]	150 uF [T520D157M006AT E055]	150 uF [T520U157M006AT E045]	150 uF [T520V157M006AT E012]
150 uF [T520C157M006AT E015]	150 uF [T520D157M008AT E025]	150 uF [T520U157M006AT E055]	150 uF [T520V157M006AT E015]

Multisim 14.0 Power Pro Components

150 uF [T520V157M006AT E018]	150 uF [T525D157M006AT E025]	1-534206-3 1-534206-7	16 pF [C2225C160KBGAC TU]
150 uF [T520V157M006AT E025]	150 uF [T525D157M010AT E025]	15C02MH-TL-E 15CGQ100	160 pF [C0402C161K1HACT U]
150 uF [T520V157M006AT E040]	150 uF [T528Z157M006AT E007]	15CLQ100 15LJQ100	160 pF [C0402C161K3HACT U]
150 uF [T520V157M006AT E045]	150 uF [T528Z157M006AT E008]	16 pF [C0603C160K2GACT U]	160 pF [C0402C161K5HACT U]
150 uF [T520V157M010AT E018]	150 uF [T528Z157M006AT E009]	16 pF [C0603C160K5GACT U]	160 pF [C0805C161K3GACT U]
150 uF [T520V157M010AT E040]	150 uF [T528Z157M006AT E012]	16 pF [C0805C160KBGAC TU]	160 pF [C0805C161K5GACT U]
150 uF [T520W157M006AT E025]	150 uF [T530D157M010AT E006]	16 pF [C1206C160KBGAC TU]	160 pF [C1206C161KBGAC TU]
150 uF [T520W157M006AT E040]	150 uF [T530D157M010AT E010]	16 pF [C1210C160KBGAC TU]	160 pF [C1210C161KBGAC TU]
150 uF [T520X157M016AT E040]	150 uF [T530X157M016AT E015]	16 pF [C1812C160KBGAC TU]	160 pF [C1812C161KBGAC TU]
150 uF [T522V157M006AT E040]	150 uF [T530X157M016AT E025]	16 pF [C1825C160KBGAC TU]	160 pF [C1825C161KBGAC TU]
150 uF [T525B157M003AT E080]	150 uF [T530X157M016AT E040]	16 pF [C2220C160KBGAC TU]	160 pF [C2220C161KBGAC TU]
	1-534206-0		

Multisim 14.0 Power Pro Components

160 pF [C2225C161KBGAC TU]	173-E37-113R001	18 nF [C0603C183K1RACT U]	18 nF [C0805C183K8RACT U]
1-640455-0	173-E37-213R001	18 nF [C0603C183K3RACT U]	18 nF [C0805C183KARACT U]
16CYQ100C	173-E50-113R001	18 nF [C0603C183K4RACT U]	18 nF [C0805F183K1RACT U]
16CYQ150C	174-E09-113R001	18 nF [C0603C183K5RACT U]	18 nF [C0805F183K3RACT U]
16SYQ060C	174-E09-213R001	18 nF [C0805C183K1RACT U]	18 nF [C0805F183K4RACT U]
16YQ045C	174-E15-113R001	18 nF [C0805C183K3HACT U]	18 nF [C1206C183K2RACT U]
16YQ150C	174-E15-213R001	18 nF [C0805C183K5HACT U]	18 nF [C1206C183K3HACT U]
171-009-113R001	174-E25-113R001	18 nF [C0402C183K8RACT U]	18 nF [C0402C183K9PACT U]
171-009-213R001	174-E25-213R001	18 nF [C0402C183K9RACT U]	18 nF [C0402C183K9RACT U]
171-015-113R001	174-E37-113R001	18 nF [C0402C183K8RACT U]	18 nF [C0402C183K8RACT U]
171-015-213R001	174-E37-213R001	18 nF [C0402C183K8RACT U]	18 nF [C0402C183K8RACT U]
171-025-113R001	174-E50-113R001	18 nF [C0402C183K8RACT U]	18 nF [C0402C183K8RACT U]
171-025-213R001	174-E50-213R001	18 nF [C0402C183K8RACT U]	18 nF [C0402C183K8RACT U]
171-037-113R001	18 nF [C0402C183K4RACT U]	18 nF [C0805C183K3GACT U]	18 nF [C1206C183K1HACT U]
171-037-213R001	18 nF [C0402C183K8PACT U]	18 nF [C0805C183K3HACT U]	18 nF [C1206C183K1RACT U]
171-050-113R001	18 nF [C0402C183K8PACT U]	18 nF [C0805C183K4RACT U]	18 nF [C1206C183K2RACT U]
171-050-213R001	18 nF [C0402C183K8RACT U]	18 nF [C0805C183K4RACT U]	18 nF [C1206C183K2RACT U]
1734035-1	18 nF [C0402C183K8RACT U]	18 nF [C0805C183K5HACT U]	18 nF [C1206C183K3GACT U]
173-E09-113R001	18 nF [C0402C183K9PACT U]	18 nF [C0805C183K5HACT U]	18 nF [C1206C183K3GACT U]
173-E09-213R001	18 nF [C0402C183K9PACT U]	18 nF [C0805C183K5HACT U]	18 nF [C1206C183K3GACT U]
173-E15-113R001	18 nF [C0402C183K9PACT U]	18 nF [C0805C183K5HACT U]	18 nF [C1206C183K3GACT U]
173-E15-213R001	18 nF [C0402C183K9PACT U]	18 nF [C0805C183K5HACT U]	18 nF [C1206C183K3GACT U]
173-E25-113R001	18 nF [C0402C183K9PACT U]	18 nF [C0805C183K5HACT U]	18 nF [C1206C183K3GACT U]
173-E25-213R001	18 nF [C0402C183K9PACT U]	18 nF [C0805C183K5HACT U]	18 nF [C1206C183K3GACT U]

Multisim 14.0 Power Pro Components

18 nF [C1206C183K5HACT U]	18 nF [C1812C183K5GACT U]	18 pF [C0603C180K5GACT U]	18 pF [C1812C180KBGAC TU]
18 nF [C1206C183K5RACT U]	18 nF [C1812C183K5HACT U]	18 pF [C0603C180K8GACT U]	18 pF [C1825C180KBGAC TU]
18 nF [C1210C183K1GACT U]	18 nF [C2220C183K2GACT U]	18 pF [C0805C180K1GACT U]	18 pF [C2220C180KBGAC TU]
18 nF [C1210C183K1HACT U]	18 nF [CA064C183K3RAC]	18 pF [C0805C180K2GACT U]	18 pF [C2225C180KBGAC TU]
18 nF [C1210C183K3HACT U]	18 nF [CDR03BX183BKSM]	18 pF [C0805C180K3GACT U]	18 uF [C1210C186K4PACT U]
18 nF [C1210C183K5GACT U]	18 pF [C0201C180K3GACT U]	18 pF [C0805C180K5GACT U]	18 uF [C1210C186K8PACT U]
18 nF [C1210C183K5HACT U]	18 pF [C0402C180K3GACT U]	18 pF [C0805C180KBGAC TU]	18 uF [C1210C186K9PACT U]
18 nF [C1210C183K5RACT U]	18 pF [C0402C180K5GACT U]	18 pF [C1206C180K1GACT U]	18 uF [T521X186M050AT E070]
18 nF [C1210C183KARACT U]	18 pF [C0402C180K8GACT U]	18 pF [C1206C180K5GACT U]	180 nF [C0603C184K4RACT U]
18 nF [C1812C183K1GACT U]	18 pF [C0603C180K2GACT U]	18 pF [C1206C180KBGAC TU]	180 nF [C0603C184K8RACT U]
18 nF [C1812C183K1HACT U]	18 pF [C0603C180K3GACT U]	18 pF [C1210C180KBGAC TU]	180 nF [C0805C184K3RACT U]

Multisim 14.0 Power Pro Components

180 nF [C0805C184K4RACT U]	180 nF [C1210C184K3HACT U]	180 nF [C1812F184K3RACT U]	180 pF [C0603C181K1RACT U]
180 nF [C0805C184K5RACT U]	180 nF [C1210C184K5RACT U]	180 nF [C1812F184K5RACT U]	180 pF [C0603C181K2RACT U]
180 nF [C0805C184K8RACT U]	180 nF [C1210F184K1RACT U]	180 nF [C1825C184K5RACT U]	180 pF [C0603C181K3RACT U]
180 nF [C1206C184K1RACT U]	180 nF [C1210F184K3RACT U]	180 nF [C2225C184K1RACT U]	180 pF [C0603C181K4RACT U]
180 nF [C1206C184K5RACT U]	180 nF [C1210F184K4RACT U]	180 pF [C0402C181K1HACT U]	180 pF [C0603C181K5GACT U]
180 nF [C1206C184M5UAC TU]	180 nF [C1210F184K5RACT U]	180 pF [C0402C181K3HACT U]	180 pF [C0603C181K5RACT U]
180 nF [C1206F184K1RACT U]	180 nF [C1812C184K1RACT U]	180 pF [C0402C181K3RACT U]	180 pF [C0603C181K8RACT U]
180 nF [C1206F184K3RACT U]	180 nF [C1812C184K5HACT U]	180 pF [C0402C181K4RACT U]	180 pF [C0805C181K1GACT U]
180 nF [C1206F184K4RACT U]	180 nF [C1812C184K5RACT U]	180 pF [C0402C181K5HACT U]	180 pF [C0805C181K2GACT U]
180 nF [C1206F184K5RACT U]	180 nF [C1812F184K1RACT U]	180 pF [C0402C181K5RACT U]	180 pF [C0805C181K5GACT U]
180 nF [C1210C184K1RACT U]	180 nF [C1812F184K2RACT U]	180 pF [C0402C181K8RACT U]	180 pF [C1206C181K1GACT U]

Multisim 14.0 Power Pro Components

180 pF [C1206C181K2GACT U]	180 uF [A700D187M002AT E018]	181-062-213R431	1G4B42
		181-078-113R431	1GH62
180 pF [C1206C181K5GACT U]	180 uF [A700D187M004AT E015]	181-078-213R431	1J4B42
		182-009-113R431	1JH62
180 pF [C1206C181KBGAC TU]	180 uF [A700D187M004AT E018]	182-009-213R431	1LH62
		182-015-113R431	1N1199C
180 pF [C1210C181KBGAC TU]	180 uF [A700D187M2R5AT E015]	182-015-213R431	1N1200C
		182-025-113R431	1N1202C
180 pF [C1812C181KBGAC TU]	180 uF [A700D187M2R5AT E018]	182-025-213R431	1N1204C
		182-037-113R431	1N1206C
180 pF [C1825C181KBGAC TU]	180 uF [A700X187M004AT E010]	182-037-213R431	1N3064
		183-009-113R161	1N3208
180 pF [C2220C181KBGAC TU]	180 uF [A700X187M006AT E010]	183-009-213R161	1N3491
		183-015-113R161	1N3492
180 pF [C2225C181KBGAC TU]	180 uF [A700X187M006AT E015]	183-015-213R161	1N3493
		183-025-113R161	1N3494
		183-025-213R161	1N3495
		183-037-113R161	1N3595
180 pF [CA064C181K4GAC TU]	181-015-113R431	183-037-213R161	1N3600
	181-015-213R431	18TQ045	1N3611GP
180 pF [CA064C181K5GAC TU]	181-026-113R431	1932258-1	1N3612GP
	181-026-213R431	1981584-1	1N3613GP
180 uF [A700D187M002AT E015]	181-044-113R431	1B4B42	1N3614GP
	181-044-213R431	1BH62	1N3659
	181-062-113R431	1DH62	1N3660

Multisim 14.0 Power Pro Components

1N3661	1N3892A	1N4003RLG	1N4151
1N3662	1N3893	1N4004	1N4152
1N3663	1N3893A	1N4004G	1N4153
1N3712	1N3899	1N4004GP	1N4154
1N3713	1N3900	1N4004RLG	1N4245GP
1N3714	1N3901	1N4005	1N4246GP
1N3715	1N3902	1N4005G	1N4247GP
1N3720	1N3903	1N4005GP	1N4248GP
1N3879	1N3909	1N4005RLG	1N4249GP
1N3879A	1N3910	1N4006	1N4305
1N3880	1N3911	1N4006FFG	1N4370A
1N3880A	1N3912	1N4006G	1N4371A
1N3881	1N3913	1N4006GP	1N4372A
1N3881A	1N3957GP	1N4006RLG	1N4383GP
1N3882	1N4001	1N4007	1N4384GP
1N3882A	1N4001G	1N4007-E3/54	1N4385GP
1N3883	1N4001GP	1N4007FFG	1N4446
1N3883A	1N4001RLG	1N4007G	1N4447
1N3889	1N4002	1N4007GP	1N4448
1N3889A	1N4002G	1N4007RLG	1N4449
1N3890	1N4002GP	1N4009	1N4454
1N3890A	1N4002RLG	1N4097	1N4461
1N3891	1N4003	1N4148	1N4462
1N3891A	1N4003G	1N4149	1N4463
1N3892	1N4003GP	1N4150	1N4464

Multisim 14.0 Power Pro Components

1N4465	1N4490	1N4732A	1N4757A
1N4466	1N4491	1N4733A	1N4758A
1N4467	1N4492	1N4734A	1N4759A
1N4468	1N4493	1N4735A	1N4760A
1N4469	1N4494	1N4736A	1N4761A
1N4470	1N4495	1N4737A	1N4762A
1N4471	1N4496	1N4738A	1N4763A
1N4472	1N4531	1N4739A	1N4764A
1N4473	1N4532	1N4740A	1N4883
1N4474	1N4534	1N4741A	1N4884
1N4475	1N4585GP	1N4742A	1N4933
1N4476	1N4586GP	1N4743A	1N4933G
1N4477	1N4678	1N4744A	1N4933GP
1N4478	1N4680	1N4745A	1N4933RLG
1N4479	1N4681	1N4746A	1N4934
1N4480	1N4684	1N4747A	1N4934G
1N4481	1N4685	1N4748A	1N4934GP
1N4482	1N4689	1N4749A	1N4934RLG
1N4483	1N4690	1N4750A	1N4935
1N4484	1N4694	1N4751A	1N4935G
1N4485	1N4697	1N4752A	1N4935GP
1N4486	1N4728A	1N4753A	1N4935RLG
1N4487	1N4729A	1N4754A	1N4936
1N4488	1N4730A	1N4755A	1N4936G
1N4489	1N4731A	1N4756A	1N4936GP

Multisim 14.0 Power Pro Components

1N4936RLG	1N4968	1N4993	1N5115
1N4937	1N4969	1N4994	1N5221B
1N4937G	1N4970	1N4995	1N5222B
1N4937GP	1N4971	1N4996	1N5223B
1N4937RLG	1N4972	1N5059	1N5224B
1N4938	1N4973	1N5059GP	1N5225B
1N4942GP	1N4974	1N5060	1N5226B
1N4944GP	1N4975	1N5060GP	1N5227B
1N4946GP	1N4976	1N5061	1N5228B
1N4947GP	1N4977	1N5061GP	1N5229B
1N4948GP	1N4978	1N5062	1N5230B
1N4954	1N4979	1N5062GP	1N5231B
1N4955	1N4980	1N5063	1N5232B
1N4956	1N4981	1N5065	1N5233B
1N4957	1N4982	1N5067	1N5234B
1N4958	1N4983	1N5069	1N5235B
1N4959	1N4984	1N5071	1N5236B
1N4960	1N4985	1N5073	1N5237B
1N4961	1N4986	1N5074	1N5238B
1N4962	1N4987	1N5077	1N5239B
1N4963	1N4988	1N5079	1N5240B
1N4964	1N4989	1N5081	1N5241B
1N4965	1N4990	1N5083	1N5242B
1N4966	1N4991	1N5085	1N5243B
1N4967	1N4992	1N5106	1N5244B

Multisim 14.0 Power Pro Components

1N5245B	1N5270B	1N5338B	1N5346BRLG
1N5246B	1N5271B	1N5338BG	1N5347B
1N5247B	1N5272B	1N5338BRLG	1N5347BG
1N5248B	1N5273B	1N5339B	1N5347BRLG
1N5249B	1N5274B	1N5339BG	1N5348B
1N5250B	1N5275B	1N5339BRLG	1N5348BG
1N5251B	1N5276B	1N5340B	1N5348BRLG
1N5252B	1N5277B	1N5340BG	1N5349B
1N5253B	1N5278B	1N5340BRLG	1N5349BG
1N5254B	1N5279B	1N5341B	1N5349BRLG
1N5255B	1N5280B	1N5341BG	1N5350B
1N5256B	1N5281B	1N5341BRLG	1N5350BG
1N5257B	1N5333B	1N5342B	1N5350BRLG
1N5258B	1N5333BRLG	1N5342BG	1N5351B
1N5259B	1N5334B	1N5342BRLG	1N5351BG
1N5260B	1N5334BRLG	1N5343B	1N5351BRLG
1N5261B	1N5335B	1N5343BG	1N5352B
1N5262B	1N5335BG	1N5343BRLG	1N5352BG
1N5263B	1N5335BRLG	1N5344B	1N5352BRLG
1N5264B	1N5336B	1N5344BG	1N5353B
1N5265B	1N5336BG	1N5344BRLG	1N5353BG
1N5266B	1N5336BRLG	1N5345B	1N5353BRLG
1N5267B	1N5337B	1N5345BRLG	1N5354B
1N5268B	1N5337BG	1N5346B	1N5355B
1N5269B	1N5337BRLG	1N5346BG	1N5355BG

Multisim 14.0 Power Pro Components

1N5355BRLG	1N5365B	1N5374BG	1N5387B
1N5356B	1N5365BG	1N5374BRLG	1N5388B
1N5356BRLG	1N5365BRLG	1N5375B	1N5388BG
1N5357B	1N5366B	1N5375BG	1N5388BRLG
1N5357BG	1N5366BG	1N5375BRLG	1N5391
1N5357BRLG	1N5366BRLG	1N5376B	1N5391GP
1N5358B	1N5367B	1N5377B	1N5392
1N5358BG	1N5367BG	1N5378B	1N5392GP
1N5358BRLG	1N5367BRLG	1N5378BG	1N5393
1N5359B	1N5368B	1N5378BRLG	1N5393GP
1N5359BG	1N5368BG	1N5379B	1N5394
1N5359BRLG	1N5368BRLG	1N5380B	1N5394GP
1N5360B	1N5369B	1N5381B	1N5395
1N5361B	1N5369BG	1N5381BRLG	1N5395GP
1N5361BG	1N5369BRLG	1N5382B	1N5396
1N5361BRLG	1N5370B	1N5383B	1N5396GP
1N5362B	1N5371B	1N5383BG	1N5397
1N5362BG	1N5371BRLG	1N5383BRLG	1N5397GP
1N5362BRLG	1N5372B	1N5384B	1N5398
1N5363B	1N5372BG	1N5384BG	1N5398GP
1N5363BG	1N5372BRLG	1N5384BRLG	1N5399
1N5363BRLG	1N5373B	1N5385B	1N5399GP
1N5364B	1N5373BG	1N5386B	1N5400
1N5364BG	1N5373BRLG	1N5386BG	1N5400G
1N5364BRLG	1N5374B	1N5386BRLG	1N5400RLG

Multisim 14.0 Power Pro Components

1N5401	1N5623GP	1N5820RLG	1N5917B
1N5401G	1N5624GP	1N5821	1N5918B
1N5401RLG	1N5625GP	1N5821G	1N5919B
1N5402	1N5626GP	1N5821RLG	1N5919BG
1N5402G	1N5627GP	1N5822	1N5919BRLG
1N5402RLG	1N5711	1N5822-E3/54	1N5920B
1N5404	1N5712	1N5822G	1N5920BG
1N5404G	1N5719	1N5822RLG	1N5921B
1N5404RLG	1N5758	1N5823	1N5921BG
1N5406	1N5758A	1N5824	1N5921BRLG
1N5406G	1N5759	1N5825	1N5922B
1N5406RLG	1N5759A	1N5826	1N5923B
1N5407G	1N5760	1N5827	1N5923BRLG
1N5407RLG	1N5761	1N5828	1N5924B
1N5408-E3/54	1N5761A	1N5829	1N5924BRLG
1N5408G	1N5767	1N5830	1N5925B
1N5408RLG	1N5817-E3/54	1N5831	1N5925BRLG
1N5450A	1N5817G	1N5832	1N5926B
1N5615GP	1N5817RLG	1N5833	1N5927B
1N5617	1N5818G	1N5834	1N5927BG
1N5617GP	1N5818RLG	1N5913B	1N5927BRLG
1N5619	1N5819G	1N5913BRLG	1N5928B
1N5619GP	1N5819RLG	1N5914B	1N5929B
1N5621	1N5820	1N5915B	1N5929BG
1N5621GP	1N5820G	1N5916B	1N5929BRLG

Multisim 14.0 Power Pro Components

1N5930B	1N5945B	1N5999B	1N6024B
1N5931B	1N5946B	1N6000B	1N6025B
1N5931BRLG	1N5946BRLG	1N6001B	1N6095
1N5932B	1N5947B	1N6002B	1N6096
1N5932BRLG	1N5948BRLG	1N6003B	1N6097
1N5933B	1N5953BG	1N6004B	1N6098
1N5934B	1N5953BRLG	1N6005B	1N6285AG
1N5934BG	1N5955BRLG	1N6006B	1N6285ARL4G
1N5934BRLG	1N5956BG	1N6007B	1N6287AG
1N5935B	1N5956BRLG	1N6008B	1N6287ARL4G
1N5935BRLG	1N5957	1N6009B	1N6292AG
1N5936B	1N5985B	1N6010B	1N6292ARL4G
1N5937B	1N5986B	1N6011B	1N6294ARL4G
1N5937BRLG	1N5987B	1N6012B	1N6373-E3/51
1N5938B	1N5988B	1N6013B	1N6478
1N5938BRLG	1N5989B	1N6014B	1N6479
1N5939B	1N5990B	1N6015B	1N6480
1N5940B	1N5991B	1N6016B	1N6481
1N5940BRLG	1N5992B	1N6017B	1N6482
1N5941B	1N5993B	1N6018B	1N6483
1N5941BRLG	1N5994B	1N6019B	1N6484
1N5942B	1N5995B	1N6020B	1N746A
1N5942BRLG	1N5996B	1N6021B	1N747A
1N5943B	1N5997B	1N6022B	1N748A
1N5944B	1N5998B	1N6023B	1N749A

Multisim 14.0 Power Pro Components

1N750A	1N966B	1N991B	1PS70SB45
1N751A	1N967B	1N992B	1PS70SB46
1N752A	1N968B	1P1S	1PS70SB82
1N753A	1N969B	1P2S	1PS70SB84
1N754A	1N970B	1P3S	1PS70SB85
1N755A	1N971B	1P4S	1PS70SB86
1N756A	1N972B	1P5S	1PS74SB23
1N757A	1N973B	1PMT12AT1G	1PS75SB45
1N758A	1N974B	1PMT16AT3G	1PS76SB10
1N759A	1N975B	1PMT33AT3G	1PS76SB17
1N914	1N976B	1PMT5.0AT1G	1PS76SB40
1N914A	1N977B	1PMT5927BT1G	1PS76SB70
1N914B	1N978B	1PS10SB82	1PS79SB10
1N916	1N979B	1PS300	1PS79SB17
1N916A	1N980B	1PS301	1PS79SB30
1N916B	1N981B	1PS302	1PS79SB31
1N957B	1N982B	1PS66SB17	1PS79SB40
1N958B	1N983B	1PS66SB82	1PS79SB70
1N959B	1N984B	1PS70SB10	1PS88SB48
1N960B	1N985B	1PS70SB14	1PS88SB82
1N961B	1N986B	1PS70SB15	1S1553
1N962B	1N987B	1PS70SB16	1S1554
1N963B	1N988B	1PS70SB20	1S1555
1N964B	1N989B	1PS70SB40	1S1830
1N965B	1N990B	1PS70SB44	1S1834

Multisim 14.0 Power Pro Components

1S1835	1SMB20CAT3G	1SMB5933BT3G	1Z11
1S1885	1SMB22CAT3G	1SMB5934BT3G	1Z12
1S1887	1SMB24AT3G	1SMB5935BT3G	1Z13
1S1888	1SMB24CAT3G	1SMB5936BT3G	1Z14
1S953	1SMB26CAT3G	1SMB5937BT3G	1Z15
1S954	1SMB28AT3G	1SMB5939BT3G	1Z30
1S955	1SMB28CAT3G	1SMB5940BT3G	1Z6.2
1SMA12CAT3G	1SMB30AT3G	1SMB70AT3G	1Z6.8
1SMA26AT3G	1SMB30CAT3G	1SMB85AT3G	1Z7.5
1SMA30AT3G	1SMB33CAT3G	1SMC28AT3G	1Z8.2
1SMA40CAT3G	1SMB36CAT3G	1SMC36AT3G	1Z9.1
1SMA5.0AT3G	1SMB5.0AT3G	1SMC6.0AT3G	1ZB10
1SMA5913BT3G	1SMB54CAT3G	1SS241	1ZB11
1SMA5918BT3G	1SMB58CAT3G	1SS268	1ZB12
1SMA5921BT3G	1SMB5914BT3G	1SS269	1ZB13
1SMA5922BT3G	1SMB5918BT3G	1SS312	1ZB14
1SMA5927BT3G	1SMB5919BT3G	1SS313	1ZB15
1SMA5931BT3G	1SMB5920BT3G	1SS314	1ZB30
1SMA5932BT3G	1SMB5921BT3G	1SS364	1ZB6.8
1SMA5936BT3G	1SMB5922BT3G	1SV218	1ZB7.5
1SMA5940BT3G	1SMB5924BT3G	1SV219	1ZB8.2
1SMB12AT3G	1SMB5925BT3G	1SV220	1ZB9.1
1SMB14AT3G	1SMB5927BT3G	1SV221	2 nF
1SMB170AT3G	1SMB5930BT3G	1SV222	[C0603C202K1HACT U]
1SMB18CAT3G	1SMB5931BT3G	1Z10	

Multisim 14.0 Power Pro Components

2 nF [C0603C202K3HACT U]	2.2 nF [C0603C222K1HACT U]	2.2 nF [C0805C222K1GACT U]	2.2 nF [C1206C222K1RACT U]
2 nF [C0603C202K5HACT U]	2.2 nF [C0603C222K1RACT U]	2.2 nF [C0805C222K1HACT U]	2.2 nF [C1206C222K2RACT U]
2 nF [C1210C202KCGAC TU]	2.2 nF [C0603C222K2RACT U]	2.2 nF [C0805C222K1RACT U]	2.2 nF [C1206C222K4RACT U]
2 nF [C1812C202KBGAC TU]	2.2 nF [C0603C222K3GACT U]	2.2 nF [C0805C222K2RACT U]	2.2 nF [C1206C222K5GACT U]
2 nF [C1825C202KBGAC TU]	2.2 nF [C0603C222K3HACT U]	2.2 nF [C0805C222K3GACT U]	2.2 nF [C1206C222K5RACT U]
2 nF [C2220C202KBGAC TU]	2.2 nF [C0603C222K3RACT U]	2.2 nF [C0805C222K3HACT U]	2.2 nF [C1210C222K1GACT U]
2 nF [C2225C202KBGAC TU]	2.2 nF [C0603C222K4RACT U]	2.2 nF [C0805C222K3RACT U]	2.2 nF [C1210C222K1RACT U]
2.2 nF [C0402C222K3RACT U]	2.2 nF [C0603C222K5HACT U]	2.2 nF [C0805C222K5HACT U]	2.2 nF [C1210C222K2GACT U]
2.2 nF [C0402C222K4RACT U]	2.2 nF [C0603C222K5RACT U]	2.2 nF [C0805C222K5RACT U]	2.2 nF [C1210C222K5GACT U]
2.2 nF [C0402C222K5RACT U]	2.2 nF [C0603C222K8RACT U]	2.2 nF [C0805C222KARACT U]	2.2 nF [C1210C222KCGAC TU]
2.2 nF [C0402C222K8RACT U]	2.2 nF [C0603C222K9RACT U]	2.2 nF [C1206C222K1GACT U]	2.2 nF [C1812C222K2GACT U]

Multisim 14.0 Power Pro Components

2.2 nF [C1812C222KBGAC TU]	2.2 uF [C0603C225K9PACT U]	2.2 uF [C1206C225K4PACT U]	2.2 uF [C1210C225K5RACT U]
2.2 nF [C1812C222KDGAC TU]	2.2 uF [C0805C225K4PACT U]	2.2 uF [C1206C225K4RACT U]	2.2 uF [C1210C225K8RACT U]
2.2 nF [C1825C222KBGAC TU]	2.2 uF [C0805C225K4RACT U]	2.2 uF [C1206C225K8PACT U]	2.2 uF [C1210C225K9PACT U]
2.2 nF [C2220C222KBGAC TU]	2.2 uF [C0805C225K8PACT U]	2.2 uF [C1206C225K8RACT U]	2.2 uF [C1210C225K9RACT U]
2.2 nF [C2225C222KBGAC TU]	2.2 uF [C0805C225K8RACT U]	2.2 uF [C1206C225K9PACT U]	2.2 uF [C1210C225M8VAC TU]
2.2 nF [CA064C222K1RACT U]	2.2 uF [C0805C225K9PACT U]	2.2 uF [C1206C225K9RACT U]	2.2 uF [C1812C225K1RACT U]
2.2 nF [CA064C222K4RACT U]	2.2 uF [C0805C225K9RACT U]	2.2 uF [C1206C225M4VAC TU]	2.2 uF [C1825C225K5RACT U]
2.2 nF [CA064C222K5RACT U]	2.2 uF [C0805C225M4VAC TU]	2.2 uF [C1210C225K1RACT U]	2.2 uF [C2220C225K5RACT U]
2.2 uF [C0402C225K9PACT U]	2.2 uF [C0805C225M8VAC TU]	2.2 uF [C1210C225K3PACT U]	2.2 uF [C2225C225K5RACT U]
2.2 uF [C0603C225K4PACT U]	2.2 uF [C1206C225K3NAC TU]	2.2 uF [C1210C225K3RACT U]	2.2 uF [C2225C225M5UAC TU]
2.2 uF [C0603C225K8PACT U]	2.2 uF [C1206C225K3PACT U]	2.2 uF [C1210C225K4RACT U]	2.2 uF [T409C225M015AH 4250]

Multisim 14.0 Power Pro Components

2.2 uF [T429A225M010AH 4250]	2.2 uF [T491D225M050AT]	2.2 uF [T498A225M010AT E4K6]	2.4 nF [C2225C242KBGAC TU]
2.2 uF [T429C225M015AH 4250]	2.2 uF [T491S225M016AT]	2.2 uF [T498B225M025AT E3K0]	2.7 nF [C0402C272K3RACT U]
2.2 uF [T491A225M006AT]	2.2 uF [T494A225M006AT]	2.4 nF [C0603C242K1HACT U]	2.7 nF [C0402C272K4RACT U]
2.2 uF [T491A225M010AT]	2.2 uF [T494A225M010AT]	2.4 nF [C0603C242K3HACT U]	2.7 nF [C0402C272K5RACT U]
2.2 uF [T491A225M016AT]	2.2 uF [T494A225M016AT]	2.4 nF [C0603C242K5HACT U]	2.7 nF [C0603C272K1HACT U]
2.2 uF [T491A225M020AT]	2.2 uF [T494A225M020AT]	2.4 nF [C0805C242K1GACT U]	2.7 nF [C0603C272K1RACT U]
2.2 uF [T491A225M025AT]	2.2 uF [T494B225M020AT]	2.4 nF [C0805C242K1HACT U]	2.7 nF [C0603C272K3GACT U]
2.2 uF [T491B225M010AT]	2.2 uF [T494B225M035AT]	2.4 nF [C0805C242K3HACT U]	2.7 nF [C0603C272K3HACT U]
2.2 uF [T491B225M020AT]	2.2 uF [T494C225M025AT]	2.4 nF [C0805C242K5HACT U]	2.7 nF [C0603C272K3RACT U]
2.2 uF [T491B225M035AT]	2.2 uF [T494C225M035AT]	2.4 nF [C1825C242KBGAC TU]	2.7 nF [C0603C272K4RACT U]
2.2 uF [T491C225M025AT]	2.2 uF [T494D225M050AT]	2.4 nF [C2220C242KBGAC TU]	2.7 nF [C0603C272K5HACT U]
2.2 uF [T491C225M035AT]	2.2 uF [T494S225M016AT]		

Multisim 14.0 Power Pro Components

2.7 nF [C0603C272K5RACT U]	2.7 nF [C0805C272K5HACT U]	2.7 nF [C1812C272K1GACT U]	2.7 uF [C1206C275K9RACT U]
2.7 nF [C0603C272K8RACT U]	2.7 nF [C0805C272K5RACT U]	2.7 nF [C1812C272K5GACT U]	2_AMP 20 pF [C0402C200K5GACT U]
2.7 nF [C0805C272K1GACT U]	2.7 nF [C0805C272KARACT U]	2.7 nF [C1825C272KBGAC TU]	20 pF [C0402C200K8GACT U]
2.7 nF [C0805C272K1HACT U]	2.7 nF [C1206C272K1GACT U]	2.7 nF [C2220C272KBGAC TU]	20 pF [C0603C200K2GACT U]
2.7 nF [C0805C272K1RACT U]	2.7 nF [C1206C272K1RACT U]	2.7 nF [C2225C272KBGAC TU]	20 pF [C0603C200K4GACT U]
2.7 nF [C0805C272K2RACT U]	2.7 nF [C1206C272K2RACT U]	2.7 uF [C0805C275K8PACT U]	20 pF [C0603C200K5GACT U]
2.7 nF [C0805C272K3GACT U]	2.7 nF [C1206C272K5GACT U]	2.7 uF [C1206C275K3PACT U]	20 pF [C0805C200K1GACT U]
2.7 nF [C0805C272K3HACT U]	2.7 nF [C1206C272K5RACT U]	2.7 uF [C1206C275K4PACT U]	20 pF [C0805C200K2GACT U]
2.7 nF [C0805C272K3RACT U]	2.7 nF [C1210C272K2GACT U]	2.7 uF [C1206C275K4RACT U]	20 pF [C0805C200K5GACT U]
2.7 nF [C0805C272K4GACT U]	2.7 nF [C1210C272K5GACT U]	2.7 uF [C1206C275K8RACT U]	20 pF [C0805C200KBGAC TU]
2.7 nF [C0805C272K4RACT U]	2.7 nF [C1210C272KCGAC TU]	2.7 uF [C1206C275K9PACT U]	20 pF [C1206C200K1GACT U]

Multisim 14.0 Power Pro Components

20 pF [C1206C200K5GACT U]	200 pF [C0603C201K5GACT U]	22 nF [C0402C223K3RACT U]	22 nF [C0603C223K8RACT U]
20 pF [C1206C200KBGAC TU]	200 pF [C0805C201K2GACT U]	22 nF [C0402C223K4RACT U]	22 nF [C0603C223M3VAC TU]
20 pF [C1206C200KCGAC TU]	200 pF [C0805C201K5GACT U]	22 nF [C0402C223K5RACT U]	22 nF [C0603C223M8VAC TU]
20 pF [C1210C200KBGAC TU]	200 pF [C1206C201K5GACT U]	22 nF [C0402C223K8PACT U]	22 nF [C0805C223K1RACT U]
20 pF [C1812C200KBGAC TU]	200 pF [C1206C201KBGAC TU]	22 nF [C0402C223K8RACT U]	22 nF [C0805C223K2RACT U]
20 pF [C1825C200KBGAC TU]	200 pF [C1210C201KBGAC TU]	22 nF [C0402C223K9PACT U]	22 nF [C0805C223K3GACT U]
20 pF [C2220C200KBGAC TU]	200 pF [C1812C201KBGAC TU]	22 nF [C0402C223K9RACT U]	22 nF [C0805C223K3HACT U]
20 pF [C2225C200KBGAC TU]	200 pF [C2220C201KBGAC TU]	22 nF [C0603C223K1RACT U]	22 nF [C0805C223K3RACT U]
20_AMP 200 pF [C0402C201K1HACT U]	200 pF [C2225C201KBGAC TU]	22 nF [C0603C223K3RACT U]	22 nF [C0805C223K4RACT U]
200 pF [C0402C201K3HACT U]	2013655-1	22 nF [C0603C223K4RACT U]	22 nF [C0805C223K5HACT U]
200 pF [C0402C201K5HACT U]	20CJQ030	22 nF [C0603C223K5RACT U]	22 nF [C0805C223K5RACT U]
	20CLQ045		
	20ETS12		

Multisim 14.0 Power Pro Components

22 nF [C0805C223K8RACT U]	22 nF [C1206C223K3HACT U]	22 nF [C1210C223K3GACT U]	22 nF [C1812C223K5HACT U]
22 nF [C0805C223KARACT U]	22 nF [C1206C223K3RACT U]	22 nF [C1210C223K3HACT U]	22 nF [C1812C223K5RACT U]
22 nF [C0805C223M5UAC TU]	22 nF [C1206C223K4RACT U]	22 nF [C1210C223K5GACT U]	22 nF [C1825C223K1GACT U]
22 nF [C0805F223K1RACT U]	22 nF [C1206C223K5HACT U]	22 nF [C1210C223K5HACT U]	22 nF [C1825C223K5GACT U]
22 nF [C0805F223K3RACT U]	22 nF [C1206C223K5RACT U]	22 nF [C1210C223K5RACT U]	22 nF [C1825C223K5RACT U]
22 nF [C0805F223K4RACT U]	22 nF [C1206C223M5UAC TU]	22 nF [C1210C223KARACT U]	22 nF [C2220C223K1GACT U]
22 nF [C0805F223K5RACT U]	22 nF [C1206F223K2RACT U]	22 nF [C1812C223K1GACT U]	22 nF [C2220C223K2GACT U]
22 nF [C1206C223K1HACT U]	22 nF [C1210C223K1GACT U]	22 nF [C1812C223K1HACT U]	22 nF [C2225C223K1GACT U]
22 nF [C1206C223K1RACT U]	22 nF [C1210C223K1HACT U]	22 nF [C1812C223K1RACT U]	22 nF [C2225C223K5GACT U]
22 nF [C1206C223K2RACT U]	22 nF [C1210C223K1RACT U]	22 nF [C1812C223K2RACT U]	22 pF [C0201C220K3GACT U]
22 nF [C1206C223K3GACT U]	22 nF [C1210C223K2RACT U]	22 nF [C1812C223K5GACT U]	22 pF [C0402C220K3GACT U]

Multisim 14.0 Power Pro Components

22 pF [C0402C220K4GACT U]	22 pF [C0805C220K5GACT U]	22 pF [C1210C220K5GACT U]	22 uF [A700D226M016AT E018]
22 pF [C0402C220K5GACT U]	22 pF [C0805C220KBGAC TU]	22 pF [C1210C220KBGAC TU]	22 uF [A700V226M006AT E028]
22 pF [C0402C220K8GACT U]	22 pF [C0805C220KCGAC TU]	22 pF [C1812C220KBGAC TU]	22 uF [A700V226M006AT E045]
22 pF [C0603C220K1GACT U]	22 pF [C0805C220KDGAC TU]	22 pF [C1825C220KBGAC TU]	22 uF [A700V226M008AT E028]
22 pF [C0603C220K2GACT U]	22 pF [C1206C220K1GACT U]	22 pF [C2220C220KBGAC TU]	22 uF [A700V226M008AT E045]
22 pF [C0603C220K3GACT U]	22 pF [C1206C220K2GACT U]	22 pF [C2225C220KBGAC TU]	22 uF [A700V226M010AT E028]
22 pF [C0603C220K4GACT U]	22 pF [C1206C220K5GACT U]	22 pF [CA064C220K2GAC TU]	22 uF [A700V226M12RAT E030]
22 pF [C0603C220K5GACT U]	22 pF [C1206C220KBGAC TU]	22 pF [CA064C220K3GAC TU]	22 uF [C0805C226K9PACT U]
22 pF [C0805C220K1GACT U]	22 pF [C1206C220KCGAC TU]	22 pF [CA064C220K4GAC TU]	22 uF [C1206C226K9PACT U]
22 pF [C0805C220K2GACT U]	22 pF [C1206C220KDGAC TU]	22 pF [CA064C220K5GAC TU]	22 uF [C1206C226M9VAC TU]
22 pF [C0805C220K3GACT U]	22 pF [C1210C220K2GACT U]	22 pF [CA064C220K8GAC TU]	22 uF [C1210C226K4PACT U]

Multisim 14.0 Power Pro Components

22 uF [C1210C226K8PACT U]	22 uF [T491B226M016AT]	22 uF [T491S226M004AT]	22 uF [T494A226M010AT]
22 uF [C1210C226K8RACT U]	22 uF [T491B226M020AT]	22 uF [T491T226M004AT]	22 uF [T494B226M004AT]
22 uF [C1210C226K9PACT U]	22 uF [T491C226M004AT]	22 uF [T491T226M006AT]	22 uF [T494B226M006AT]
22 uF [C1210C226K9PACT U]	22 uF [T491C226M006AT]	22 uF [T491T226M010AT]	22 uF [T494B226M010AT]
22 uF [C1210C226K9RACT U]	22 uF [T491C226M010AT]	22 uF [T491U226M006AT]	22 uF [T494B226M016AT]
22 uF [C1210C226M8VAC TU]	22 uF [T491C226M016AT]	22 uF [T491U226M010AT]	22 uF [T494B226M020AT]
22 uF [T419G226M020AH 4250]	22 uF [T491C226M020AT]	22 uF [T491U226M016AT]	22 uF [T494C226M004AT]
22 uF [T429D226M006AH 4250]	22 uF [T491C226M025AT]	22 uF [T491U226M016AT]	22 uF [T494C226M006AT]
22 uF [T491A226M004AT]	22 uF [T491D226M010AT]	22 uF [T491V226M020AT]	22 uF [T494C226M010AT]
22 uF [T491A226M006AT]	22 uF [T491D226M016AT]	22 uF [T491V226M025AT]	22 uF [T494C226M016AT]
22 uF [T491A226M010AT]	22 uF [T491D226M020AT]	22 uF [T491X226M035AT]	22 uF [T494C226M020AT]
22 uF [T491B226M004AT]	22 uF [T491D226M025AT]	22 uF [T491X226M050AT]	22 uF [T494C226M025AT]
22 uF [T491B226M006AT]	22 uF [T491D226M025AT]	22 uF [T493X226M025AH 6110]	22 uF [T494D226M010AT]
22 uF [T491B226M010AT]	22 uF [T491D226M035AT]	22 uF [T494A226M004AT]	22 uF [T494D226M016AT]
		22 uF [T494A226M006AT]	

Multisim 14.0 Power Pro Components

22 uF [T494D226M020AT]	22 uF [T494X226M050AT]	22 uF [T495X226M035AT E200]	22 uF [T510X226M035AT E080]
22 uF [T494D226M025AT]	22 uF [T495C226M025AT E300]	22 uF [T495X226M035AT E275]	22 uF [T510X226M035AT E100]
22 uF [T494D226M035AT]	22 uF [T495C226M025AT E900]	22 uF [T497D226M006AT 6110]	22 uF [T520A226M006AT E090]
22 uF [T494S226M004AT]	22 uF [T495D226M020AT E180]	22 uF [T498B226M010AT E1K5]	22 uF [T520A226M006AT E100]
22 uF [T494T226M004AT]	22 uF [T495D226M020AT E225]	22 uF [T498C226M006AT E1K3]	22 uF [T520A226M010AT E080]
22 uF [T494T226M006AT]	22 uF [T495D226M025AT E200]	22 uF [T498C226M010AT E1K1]	22 uF [T520C226M016AT E080]
22 uF [T494U226M006AT]	22 uF [T495D226M035AT E125]	22 uF [T498C226M016AT E1K0]	22 uF [T520T226M008AT E070]
22 uF [T494U226M010AT]	22 uF [T495D226M035AT E200]	22 uF [T498D226M025AT E600]	22 uF [T520V226M020AT E045]
22 uF [T494U226M016AT]	22 uF [T495D226M035AT E300]	22 uF [T498X226M035AT E500]	22 uF [T520V226M020AT E090]
22 uF [T494V226M020AT]	22 uF [T495X226M025AT E225]	22 uF [T499D226M016AT E800]	22 uF [T521V226M025AT E060]
22 uF [T494V226M025AT]	22 uF [T495X226M035AT E125]	22 uF [T510X226M035AT E060]	22 uF [T525B226M010AT E080]
22 uF [T494X226M035AT]			

Multisim 14.0 Power Pro Components

22 uF [T541X226M050AH 6510]	220 nF [C0805C224K4RACT U]	220 nF [C1206F224K4RACT U]	220 nF [C1812C224K1RACT U]
220 nF [C0402C224K9PACT U]	220 nF [C0805C224K5RACT U]	220 nF [C1206F224K5RACT U]	220 nF [C1812C224K5HACT U]
220 nF [C0603C224K3RACT U]	220 nF [C0805C224K8RACT U]	220 nF [C1210C224K1RACT U]	220 nF [C1812C224K5RACT U]
220 nF [C0603C224K4RACT U]	220 nF [C0805C224M3VAC TU]	220 nF [C1210C224K3GACT U]	220 nF [C1812C224KARACT U]
220 nF [C0603C224K8NAC TU]	220 nF [C0805C224M4VAC TU]	220 nF [C1210C224K3RACT U]	220 nF [C1812C224M5UAC TU]
220 nF [C0603C224K8RACT U]	220 nF [C1206C224K1RACT U]	220 nF [C1210C224K5RACT U]	220 nF [C1812F224K1RACT U]
220 nF [C0603C224K9RACT U]	220 nF [C1206C224K3RACT U]	220 nF [C1210C224M5UAC TU]	220 nF [C1812F224K2RACT U]
220 nF [C0603C224M3VAC TU]	220 nF [C1206C224K4RACT U]	220 nF [C1210F224K1RACT U]	220 nF [C1812F224K3RACT U]
220 nF [C0603C224M4VAC TU]	220 nF [C1206C224K5RACT U]	220 nF [C1210F224K3RACT U]	220 nF [C1812F224K5RACT U]
220 nF [C0603C224M8VAC TU]	220 nF [C1206C224M5UAC TU]	220 nF [C1210F224K4RACT U]	220 nF [C1825C224K1RACT U]
220 nF [C0805C224K3RACT U]	220 nF [C1206F224K3RACT U]	220 nF [C1210F224K5RACT U]	220 nF [C1825C224K2RACT U]

Multisim 14.0 Power Pro Components

220 nF [C1825C224K5RACT U]	220 nF [T494B224M050AT]	220 pF [C0603C221K2RACT U]	220 pF [C0805C221K2RACT U]
220 nF [C1825C224M1UAC TU]	220 nF [T499A224M035AT E18K]	220 pF [C0603C221K3GACT U]	220 pF [C0805C221K3GACT U]
220 nF [C1825C224M5UAC TU]	220 pF [C0402C221K1HACT U]	220 pF [C0603C221K3RACT U]	220 pF [C0805C221K3RACT U]
220 nF [C2220C224K1GACT U]	220 pF [C0402C221K3HACT U]	220 pF [C0603C221K4GACT U]	220 pF [C0805C221K4RACT U]
220 nF [C2220C224K5GACT U]	220 pF [C0402C221K3RACT U]	220 pF [C0603C221K4RACT U]	220 pF [C0805C221K5GACT U]
220 nF [C2225C224K1RACT U]	220 pF [C0402C221K4RACT U]	220 pF [C0603C221K5GACT U]	220 pF [C0805C221K5RACT U]
220 nF [C2225C224K5RACT U]	220 pF [C0402C221K5GACT U]	220 pF [C0603C221K5RACT U]	220 pF [C0805C221K8RACT U]
220 nF [T409A224M035AH 4250]	220 pF [C0402C221K5HACT U]	220 pF [C0603C221K8RACT U]	220 pF [C0805C221KARACT U]
220 nF [T491A224M035AT]	220 pF [C0402C221K5RACT U]	220 pF [C0805C221K1GACT U]	220 pF [C1206C221K1GACT U]
220 nF [T491B224M050AT]	220 pF [C0402C221K8RACT U]	220 pF [C0805C221K1RACT U]	220 pF [C1206C221K2GACT U]
220 nF [T493B224M050AH 6120]	220 pF [C0603C221K1RACT U]	220 pF [C0805C221K2GACT U]	220 pF [C1206C221K5GACT U]
220 nF [T494A224M035AT]			

Multisim 14.0 Power Pro Components

220 pF [C1206C221KBGAC TU]	220 uF [A700D227M002AT E015]	220 uF [T491D227M010AT]	220 uF [T494E227M016AT]
220 pF [C1206C221KCGAC TU]	220 uF [A700D227M002AT E018]	220 uF [T491D227M2R5AT]	220 uF [T494V227M004AT]
220 pF [C1206C221KDGAC TU]	220 uF [A700D227M004AT E009]	220 uF [T491E227M016AT]	220 uF [T494X227M006AT]
220 pF [C1210C221K1GACT U]	220 uF [A700V227M002AT E009]	220 uF [T491V227M004AT]	220 uF [T494X227M010AT]
220 pF [C1210C221KBGAC TU]	220 uF [A700X227M004AT E010]	220 uF [T491V227M006AT]	220 uF [T494X227M016AT]
220 pF [C1812C221KBGAC TU]	220 uF [A700X227M004AT E010]	220 uF [T491X227M006AT]	220 uF [T495C227M006AT E225]
220 pF [C1812C221KBGAC TU]	220 uF [A700X227M004AT E015]	220 uF [T491X227M010AT]	220 uF [T495D227M004AT E040]
220 pF [C1825C221KBGAC TU]	220 uF [A700X227M2R5AT E010]	220 uF [T491X227M016AT]	220 uF [T495D227M004AT E050]
220 pF [C2220C221KBGAC TU]	220 uF [A700X227M2R5AT E015]	220 uF [T494C227M006AT]	220 uF [T495D227M004AT E100]
220 pF [C2225C221KBGAC TU]	220 uF [T419H227M004AH 4250]	220 uF [T494D227M006AT]	220 uF [T495D227M006AT E045]
220 pF [CA064C221K5GAC TU]	220 uF [T491B227M004AT]	220 uF [T494D227M010AT]	220 uF [T495D227M006AT E100]
220 pF [CDR02BP221BKSM]	220 uF [T491C227M006AT]	220 uF [T494D227M2R5AT]	220 uF [T495D227M010AT E045]
	220 uF [T491D227M006AT]		

Multisim 14.0 Power Pro Components

220 uF [T495D227M010AT E075]	220 uF [T495X227M010AT E070]	220 uF [T520B227M004AT E070]	220 uF [T520C227M004AT E055]
220 uF [T495D227M010AT E100]	220 uF [T495X227M010AT E100]	220 uF [T520B227M006AT E035]	220 uF [T520C227M006AT E025]
220 uF [T495D227M010AT E125]	220 uF [T495X227M016AT E100]	220 uF [T520B227M2R5AT E015]	220 uF [T520C227M006AT E045]
220 uF [T495D227M2R5AT E045]	220 uF [T496X227M010AT 6110]	220 uF [T520B227M2R5AT E018]	220 uF [T520C227M2R5AT E025]
220 uF [T495E227M016AT E050]	220 uF [T498X227M010AT E500]	220 uF [T520B227M2R5AT E025]	220 uF [T520D227M004AT E012]
220 uF [T495E227M016AT E075]	220 uF [T510X227M016AT E025]	220 uF [T520B227M2R5AT E030]	220 uF [T520D227M004AT E065]
220 uF [T495E227M016AT E150]	220 uF [T510X227M016AT E040]	220 uF [T520B227M2R5AT E035]	220 uF [T520D227M006AT E006]
220 uF [T495X227M006AT E100]	220 uF [T513X227M016AH 6110]	220 uF [T520B227M2R5AT E070]	220 uF [T520D227M006AT E007]
220 uF [T495X227M010AT E045]	220 uF [T513X227M016AH 6120]	220 uF [T520C227M004AT E018]	220 uF [T520D227M006AT E009]
220 uF [T495X227M010AT E050]	220 uF [T520B227M004AT E035]	220 uF [T520C227M004AT E025]	220 uF [T520D227M006AT E015]
220 uF [T495X227M010AT E060]	220 uF [T520B227M004AT E045]	220 uF [T520C227M004AT E045]	220 uF [T520D227M006AT E040]

Multisim 14.0 Power Pro Components

220 uF [T520D227M006AT E050]	220 uF [T520V227M004AT E015]	220 uF [T520V227M006AT E040]	220 uF [T522V227M006AT E025]
220 uF [T520D227M010AT E018]	220 uF [T520V227M004AT E018]	220 uF [T520V227M010AT E045]	220 uF [T522V227M006AT E040]
220 uF [T520D227M010AT E025]	220 uF [T520V227M004AT E025]	220 uF [T520V227M2R5AT E007]	220 uF [T525D227M004AT E025]
220 uF [T520D227M010AT E040]	220 uF [T520V227M004AT E040]	220 uF [T520V227M2R5AT E009]	220 uF [T525D227M006AT E025]
220 uF [T520D227M2R5AT E007]	220 uF [T520V227M004AT E045]	220 uF [T520V227M2R5AT E012]	220 uF [T525D227M010AT E025]
220 uF [T520D227M2R5AT E040]	220 uF [T520V227M006AT E007]	220 uF [T520V227M2R5AT E015]	220 uF [T528Z227M004AT E007]
220 uF [T520U227M2R5AT E055]	220 uF [T520V227M006AT E009]	220 uF [T520V227M2R5AT E025]	220 uF [T528Z227M004AT E009]
220 uF [T520V227M004AT E006]	220 uF [T520V227M006AT E012]	220 uF [T520V227M2R5AT E045]	220 uF [T528Z227M004AT E012]
220 uF [T520V227M004AT E007]	220 uF [T520V227M006AT E015]	220 uF [T520W227M004AT E025]	220 uF [T528Z227M006AT E009]
220 uF [T520V227M004AT E009]	220 uF [T520V227M006AT E018]	220 uF [T520W227M004AT E040]	220 uF [T528Z227M006AT E012]
220 uF [T520V227M004AT E012]	220 uF [T520V227M006AT E025]	220 uF [T520Y227M010AT E040]	220 uF [T530D227M006AT E005]

Multisim 14.0 Power Pro Components

220 uF [T530D227M006AT E006]	24 pF [C1206C240KBGAC TU]	240 pF [C0805C241K5GACT U]	27 nF [C0402C273K4RACT U]
220 uF [T530D227M010AT E006]	24 pF [C1210C240KBGAC TU]	240 pF [C1206C241KBGAC TU]	27 nF [C0402C273K8PACT U]
220 uF [T530D227M010AT E010]	24 pF [C1812C240KBGAC TU]	240 pF [C1210C241KBGAC TU]	27 nF [C0402C273K8RACT U]
220 uF [T530Y227M010AT E006]	24 pF [C1825C240KBGAC TU]	240 pF [C1812C241KBGAC TU]	27 nF [C0402C273K9PACT U]
220 uF [T541D227M010AH 6510]	24 pF [C1825C240KCGAC TU]	240 pF [C1825C241KBGAC TU]	27 nF [C0402C273K9RACT U]
220 uF [T543V227M004AT E015]	24 pF [C2220C240KBGAC TU]	240 pF [C2220C241KBGAC TU]	27 nF [C0603C273K1RACT U]
22GQ100	24 pF [C2225C240KBGAC TU]	240 pF [C2225C241KBGAC TU]	27 nF [C0603C273K3RACT U]
24 pF [C0402C240K4GACT U]	240 pF [C0402C241K1HACT U]	25_AMP 2-534206-0	27 nF [C0603C273K4RACT U]
24 pF [C0402C240K5GACT U]	240 pF [C0402C241K3HACT U]	27 mF [C0402C279K5GACT U]	27 nF [C0603C273K5RACT U]
24 pF [C0603C240K2GACT U]	240 pF [C0402C241K5HACT U]	27 mF [C0805C279KBGAC TU]	27 nF [C0805C273K1RACT U]
24 pF [C0805C240K5GACT U]	240 pF [C0603C241K5GACT U]	27 nF [C0402C273K3RACT U]	27 nF [C0805C273K2RACT U]
24 pF [C0805C240KBGAC TU]			

Multisim 14.0 Power Pro Components

27 nF [C0805C273K3HACT U]	27 nF [C1206C273K1RACT U]	27 nF [C1210C273K5GACT U]	27 pF [C0201C270K3GACT U]
27 nF [C0805C273K3RACT U]	27 nF [C1206C273K3HACT U]	27 nF [C1210C273K5HACT U]	27 pF [C0402C270K3GACT U]
27 nF [C0805C273K4RACT U]	27 nF [C1206C273K5HACT U]	27 nF [C1210C273K5RACT U]	27 pF [C0402C270K4GACT U]
27 nF [C0805C273K5RACT U]	27 nF [C1206C273K5RACT U]	27 nF [C1210C273KARACT U]	27 pF [C0402C270K5GACT U]
27 nF [C0805C273K8RACT U]	27 nF [C1206C273KARACT U]	27 nF [C1812C273K1HACT U]	27 pF [C0402C270K8GACT U]
27 nF [C0805C273M5UAC TU]	27 nF [C1210C273K1GACT U]	27 nF [C1812C273K1RACT U]	27 pF [C0603C270K1GACT U]
27 nF [C0805F273K1RACT U]	27 nF [C1210C273K1HACT U]	27 nF [C1812C273K5HACT U]	27 pF [C0603C270K2GACT U]
27 nF [C0805F273K3RACT U]	27 nF [C1210C273K1RACT U]	27 nF [C1825C273K1GACT U]	27 pF [C0603C270K5GACT U]
27 nF [C0805F273K4RACT U]	27 nF [C1210C273K2RACT U]	27 nF [C1825C273K5GACT U]	27 pF [C0805C270K1GACT U]
27 nF [C0805F273K5RACT U]	27 nF [C1210C273K3GACT U]	27 nF [C2220C273K1GACT U]	27 pF [C0805C270K2GACT U]
27 nF [C1206C273K1HACT U]	27 nF [C1210C273K3HACT U]	27 nF [C2220C273K2GACT U]	27 pF [C0805C270K5GACT U]

Multisim 14.0 Power Pro Components

27 pF [C0805C270KBGAC TU]	27 pF [C2225C270KBGAC TU]	270 nF [C0805C274K8RACT U]	270 nF [C1210C274M5UAC TU]
27 pF [C0805C270KDGAC TU]	27 pF [CA064C270K5GAC TU]	270 nF [C1206C274K1RACT U]	270 nF [C1210F274K1RACT U]
27 pF [C1206C270K1GACT U]	27 pF [CA064C270K8GAC TU]	270 nF [C1206C274K3RACT U]	270 nF [C1210F274K3RACT U]
27 pF [C1206C270K2GACT U]	270 nF [C0603C274K4PACT U]	270 nF [C1206C274K4RACT U]	270 nF [C1210F274K4RACT U]
27 pF [C1206C270K5GACT U]	270 nF [C0603C274K4RACT U]	270 nF [C1206C274K5RACT U]	270 nF [C1210F274K5RACT U]
27 pF [C1206C270KBGAC TU]	270 nF [C0603C274K8PACT U]	270 nF [C1206F274K3RACT U]	270 nF [C1812C274K1RACT U]
27 pF [C1210C270KBGAC TU]	270 nF [C0603C274K8RACT U]	270 nF [C1206F274K4RACT U]	270 nF [C1812C274K5RACT U]
27 pF [C1812C270KBGAC TU]	270 nF [C0603C274K9PACT U]	270 nF [C1206F274K5RACT U]	270 nF [C1812C274KARACT U]
27 pF [C1812C270KHGAC TU]	270 nF [C0603C274K9RACT U]	270 nF [C1210C274K1RACT U]	270 nF [C1812F274K1RACT U]
27 pF [C1825C270KBGAC TU]	270 nF [C0805C274K3RACT U]	270 nF [C1210C274K3RACT U]	270 nF [C1812F274K2RACT U]
27 pF [C2220C270KBGAC TU]	270 nF [C0805C274K4RACT U]	270 nF [C1210C274K5RACT U]	270 nF [C1812F274K3RACT U]

Multisim 14.0 Power Pro Components

270 nF [C1812F274K5RACT U]	270 pF [C0402C271K3RACT U]	270 pF [C0603C271K5GACT U]	270 pF [C1206C271K5GACT U]
270 nF [C1825C274K1RACT U]	270 pF [C0402C271K4RACT U]	270 pF [C0603C271K5RACT U]	270 pF [C1206C271KBGAC TU]
270 nF [C1825C274K5RACT U]	270 pF [C0402C271K5GACT U]	270 pF [C0805C271K1GACT U]	270 pF [C1210C271KBGAC TU]
270 nF [C2220C274K1GACT U]	270 pF [C0402C271K5HACT U]	270 pF [C0805C271K1RACT U]	270 pF [C1812C271KBGAC TU]
270 nF [C2220C274K5GACT U]	270 pF [C0402C271K5RACT U]	270 pF [C0805C271K2GACT U]	270 pF [C1825C271KBGAC TU]
270 nF [C2220C274K5RACT U]	270 pF [C0402C271K8RACT U]	270 pF [C0805C271K2RACT U]	270 pF [C2220C271KBGAC TU]
270 nF [C2225C274K1RACT U]	270 pF [C0603C271K1RACT U]	270 pF [C0805C271K4RACT U]	270 pF [C2225C271KBGAC TU]
270 nF [C2225C274K2RACT U]	270 pF [C0603C271K2RACT U]	270 pF [C0805C271K5GACT U]	270 uF [A700X277M002AT E010]
270 nF [C2225C274K5RACT U]	270 pF [C0603C271K3RACT U]	270 pF [C0805C271K5RACT U]	270 uF [A700X277M002AT E015]
270 pF [C0402C271K1HACT U]	270 pF [C0603C271K4GACT U]	270 pF [C1206C271K1GACT U]	270 uF [A700X277M004AT E010]
270 pF [C0402C271K3HACT U]	270 pF [C0603C271K4RACT U]	270 pF [C1206C271K2GACT U]	270 uF [A700X277M004AT E015]

27C010N120

Multisim 14.0 Power Pro Components

27C010N150	27C040V150	27C256-12L	27C512N90
27C010N70	27C128-12L	27C256-12P	27C512Q120
27C010N90	27C128-12P	27C256-15L	27C512Q150
27C010Q120	27C128-15L	27C256-15P	27C512Q90
27C010Q150	27C128-15P	27C256-20L	27C512V120
27C010Q70	27C128-17L	27C256-20P	27C512V150
27C010Q90	27C128-17P	27C256N100	27C512V90
27C010V120	27C128-20L	27C256N120	27C64-12L
27C010V150	27C128-20P	27C256N150	27C64-12P
27C010V70	27C128-25L	27C256N200	27C64-15L
27C010V90	27C128-25P	27C256N90	27C64-15P
27C020N100	27C128N120	27C256Q100	27C64-17L
27C020N120	27C128N150	27C256Q120	27C64-17P
27C020N150	27C128N200	27C256Q150	27C64-20L
27C020Q100	27C128N90	27C256Q200	27C64-20P
27C020Q120	27C128Q120	27C256Q90	27C64-25L
27C020Q150	27C128Q150	27C256V100	27C64-25P
27C020V100	27C128Q200	27C256V120	27C64E200-883
27C020V120	27C128Q90	27C256V150	27C64E250-883
27C020V150	27C128V120	27C256V200	27C64E350-883
27C040N120	27C128V150	27C256V90	27C64N150
27C040N150	27C128V200	27C32BQ150	27C64N200
27C040Q120	27C128V90	27C32BQ200	27C64Q150
27C040Q150	27C16BQ150	27C512N120	27C64Q200
27C040V120	27C16BQ200	27C512N150	27C64Q200-883

Multisim 14.0 Power Pro Components

27C64Q250-883	2N1778	2N2904A	2N3393
27C64Q350-883	2N2102	2N2905	2N3394
282834-2	2N2218	2N2905A	2N3414
282834-4	2N2218A	2N2906	2N3415
282834-5	2N2219	2N2906A	2N3416
282834-8	2N2219A	2N2907	2N3417
28V_7.5W	2N2221	2N2907A	2N3439
292303-1	2N2221A	2N2923	2N3441
292304-1	2N2222	2N2924	2N3442G
2A3	2N2222A	2N2925	2N3458
2K8RAM	2N2369	2N3019	2N3459
2N1132A	2N2369A	2N3020	2N3485
2N1595	2N2573	2N3055A	2N3485A
2N1596	2N2574	2N3055AG	2N3486
2N1597	2N2575	2N3055G	2N3486A
2N1599	2N2576	2N3244	2N3494
2N1711	2N2577	2N3250	2N3495
2N1770	2N2578	2N3250A	2N3501
2N1771	2N2579	2N3251	2N3634
2N1772	2N2608	2N3251A	2N3635
2N1773	2N2609	2N3370	2N3636
2N1774	2N2619	2N3390	2N3637
2N1775	2N2712	2N3391	2N3649
2N1776	2N2714	2N3391A	2N3650
2N1777	2N2904	2N3392	2N3651

Multisim 14.0 Power Pro Components

2N3652	2N3823	2N3954A	2N4126
2N3653	2N3824	2N3955	2N4167
2N3654	2N3858A	2N3955A	2N4168
2N3655	2N3859	2N3956	2N4169
2N3656	2N3859A	2N3957	2N4170
2N3657	2N3860	2N3958	2N4171
2N3658	2N3870	2N3966	2N4172
2N3668	2N3871	2N3967	2N4173
2N3669	2N3872	2N3970	2N4174
2N3670	2N3873	2N3971	2N4183
2N3684	2N3879	2N3972	2N4184
2N3685	2N3896	2N4014	2N4185
2N3686	2N3897	2N4058	2N4186
2N3687	2N3898	2N4061	2N4187
2N3700	2N3899	2N4062	2N4188
2N3702	2N3903	2N4084	2N4189
2N3703	2N3904	2N4091	2N4190
2N3707	2N3904G	2N4092	2N4199
2N3711	2N3905	2N4093	2N4200
2N3771G	2N3906	2N4117A	2N4201
2N3772G	2N3906G	2N4118A	2N4202
2N3773G	2N3921	2N4119A	2N4203
2N3792	2N3922	2N4123	2N4204
2N3821	2N3947	2N4124	2N4220
2N3822	2N3954	2N4125	2N4220A

Multisim 14.0 Power Pro Components

2N4221	2N4407	2N4919G	2N5064
2N4221A	2N4409	2N4920	2N5078
2N4222	2N4410	2N4920G	2N5086
2N4222A	2N4416	2N4921	2N5087
2N4223	2N4416A	2N4921G	2N5088
2N4264	2N4424	2N4922	2N5089
2N4265	2N4441	2N4922G	2N5103
2N4286	2N4442	2N4923	2N5105
2N4289	2N4443	2N4923G	2N5114
2N4291	2N4444	2N5018	2N5115
2N4338	2N4856	2N5019	2N5116
2N4339	2N4856A	2N5020	2N5168
2N4340	2N4857	2N5021	2N5169
2N4341	2N4857A	2N5038	2N5170
2N4381	2N4858	2N5038G	2N5171
2N4391	2N4858A	2N5039	2N5172
2N4392	2N4859	2N5045	2N5191
2N4393	2N4859A	2N5046	2N5191G
2N4398	2N4860	2N5047	2N5192
2N4399	2N4860A	2N5058	2N5192G
2N4400	2N4861	2N5059	2N5194
2N4401	2N4861A	2N5060	2N5194G
2N4402	2N4918	2N5061	2N5195
2N4403	2N4918G	2N5062	2N5195G
2N4405	2N4919	2N5063	2N5196

Multisim 14.0 Power Pro Components

2N5197	2N5400	2N5524	2N5684
2N5198	2N5401	2N5545	2N5684G
2N5199	2N5415	2N5550	2N5685
2N5204	2N5416	2N5550G	2N5686
2N5205	2N5432	2N5550RLRPG	2N5686G
2N5206	2N5433	2N5551	2N5745
2N5207	2N5434	2N5556	2N5769
2N5209	2N5444	2N5557	2N5771
2N5210	2N5445	2N5558	2N5817
2N5223	2N5446	2N5564	2N5830
2N5224	2N5447	2N5565	2N5838
2N5226	2N5452	2N5566	2N5879
2N5227	2N5454	2N5567	2N5880
2N5232	2N5484	2N5568	2N5881
2N5232A	2N5485	2N5571	2N5882
2N5302	2N5486	2N5572	2N5883
2N5302G	2N5515	2N5581	2N5883G
2N5303	2N5516	2N5629	2N5884
2N5354	2N5517	2N5655	2N5884G
2N5355	2N5518	2N5655G	2N5885
2N5358	2N5519	2N5656	2N5885G
2N5365	2N5520	2N5657	2N5886
2N5366	2N5521	2N5657G	2N5886G
2N5397	2N5522	2N5671	2N5911
2N5398	2N5523	2N5672	2N5912

Multisim 14.0 Power Pro Components

2N6027	2N6108	2N6168	2N6346
2N6027G	2N6109	2N6169	2N6347
2N6027RL1G	2N6109G	2N6170	2N6348
2N6027RLRAG	2N6110	2N6171	2N6349
2N6028	2N6111	2N6172	2N6350
2N6028G	2N6111G	2N6173	2N6351
2N6028RLRAG	2N6121	2N6174	2N6352
2N6028RLRMG	2N6122	2N6211	2N6353
2N6028RLRPG	2N6123	2N6213	2N6379
2N6034G	2N6124	2N6214	2N6387G
2N6035G	2N6125	2N6251	2N6388G
2N6036G	2N6126	2N6274	2N6394
2N6038	2N6145	2N6275	2N6395
2N6038G	2N6146	2N6284G	2N6396
2N6039G	2N6147	2N6286G	2N6397
2N6040G	2N6157	2N6287G	2N6398
2N6042G	2N6158	2N6288	2N6399
2N6043G	2N6159	2N6288G	2N6400
2N6045G	2N6160	2N6292G	2N6401
2N6052G	2N6161	2N6338G	2N6402
2N6071	2N6162	2N6341G	2N6403
2N6073BG	2N6163	2N6342	2N6404
2N6106	2N6164	2N6343	2N6405
2N6107	2N6165	2N6344	2N6420
2N6107G	2N6167	2N6345	2N6421

Multisim 14.0 Power Pro Components

2N6422	2N6506	2N6675	2N6760
2N6423	2N6507	2N6676	2N6761
2N6426	2N6508	2N6677	2N6762
2N6427	2N6509	2N6678	2N6763
2N6436	2N6515	2N6686	2N6764
2N6437	2N6516	2N6687	2N6765
2N6438	2N6517	2N6688	2N6766
2N6473	2N6519	2N6702	2N6767
2N6474	2N6520	2N6703	2N6768
2N6475	2N6542	2N6704	2N6769
2N6476	2N6544	2N6714	2N6770
2N6486	2N6545	2N6715	2N6771
2N6487	2N6546	2N6727	2N6772
2N6487G	2N6659	2N6738	2N6773
2N6488	2N6660	2N6739	2N6782
2N6488G	2N6660JANTX	2N6740	2N6784
2N6489	2N6660JANTXV	2N6751	2N6786
2N6490	2N6661	2N6752	2N6788
2N6490G	2N6661JANTX	2N6753	2N6790
2N6491	2N6661JANTXV	2N6754	2N6792
2N6491G	2N6667G	2N6755	2N6794
2N6497	2N6671	2N6756	2N6796
2N6498	2N6672	2N6757	2N6798
2N6504	2N6673	2N6758	2N6800
2N6505	2N6674	2N6759	2N6802

Multisim 14.0 Power Pro Components

2N6804	2N7002BK	2N7073	2P5S
2N681	2N7002BKM	2N7074	2PA1576Q
2N682	2N7002BKMB	2N7075	2PA1576R
2N6823	2N7002BKS	2N7076	2PA1576S
2N683	2N7002BKT	2N7077	2PA1774Q
2N6849	2N7002BKV	2N7078	2PA1774QM
2N685	2N7002BKW	2N708	2PA1774QMB
2N6851	2N7002CK	2N7081	2PA1774R
2N687	2N7002DW	2N7082	2PA1774RM
2N688	2N7002E	2N7085	2PA1774RMB
2N689	2N7002ET1G	2N7086	2PA1774S
2N690	2N7002F	2N718A	2PA1774SM
2N691	2N7002K	2N720A	2PA1774SMB
2N692	2N7002LT1	2N7269	2PB1219AQ
2N6975	2N7002LT1G	2N834	2PB1219AR
2N6976	2N7002LT3G	2N869A	2PB1219AS
2N6977	2N7002P	2N910	2PB1424
2N6978	2N7002PS	2N914	2PB709ARL
2N699	2N7002PT	2N930	2PB709ART
2N7000	2N7002PV	2N930A	2PB709ARW
2N7000_SILI	2N7002PW	2N956	2PB709ASL
2N7000G	2N7012	2P1S	2PB709ASW
2N7000RLRAG	2N706	2P2S	2PB709BRL
2N7002	2N7071	2P3S	2PB709BSL
2N7002_SILI	2N7072	2P4S	2PB710ARL

Multisim 14.0 Power Pro Components

2PB710ASL	2SA1213	2SC2655	2SD1502
2PC4081Q	2SA1416S-TD-E	2SC2786	2SD1536M
2PC4081R	2SA1416T-TD-E	2SC2873	2SD1623S-TD-E
2PC4081S	2SA1460	2SC3030	2SD1623T-TD-E
2PC4617Q	2SA1507S	2SC3649S-TD-E	2SD1628F-TD-E
2PC4617QM	2SA1507T	2SC3649S-TD-H	2SD1628F-TD-H
2PC4617QMB	2SA1627	2SC3649T-TD-E	2SD1628G-TD-E
2PC4617R	2SA1774G	2SC3649T-TD-H	2SD1628G-TD-H
2PC4617RM	2SA1774T1G	2SC3733	2SD1740
2PC4617RMB	2SA2126-E	2SC4341	2SD1805F-E
2PD1820AR	2SA2126-H	2SC4617G	2SD1805F-TL-E
2PD1820AS	2SA2126-TL-E	2SC4617T1G	2SD1805G-E
2PD2150	2SA2126-TL-H	2SC5060	2SD1805G-TL-E
2PD601ARL	2SA2205-E	2SC5566-TD-E	2SD1815S-E
2PD601ART	2SA2205-TL-E	2SC5658M3T5G	2SD1815S-TL-E
2PD601ARW	2SA733	2SC5706-E	2SD1815T-E
2PD601ASL	2SA952	2SC5706-H	2SD1815T-TL-E
2PD601ASW	2SA953	2SC5706-TL-E	2SD1861
2PD601BRL	2SA954	2SC5706-TL-H	2SD947
2PD601BSL	2SB1205S-TL-E	2SC5964-TD-E	2SD983
2PD602AQL	2SB1205T-TL-E	2SC5964-TD-H	2SJ108
2PD602ARL	2SC1815	2SC945	2SJ108BL
2PD602ASL	2SC2001	2SD1073	2SJ108GR
2SA1015	2SC2120	2SD1128	2SJ108V
2SA1020	2SC2240	2SD1379	2SJ517

Multisim 14.0 Power Pro Components

2SJ652	2SK3233	3 nF [C0603C302K5HACT U]	3.3 nF [C0402C332K5RACT U]
2SJ652-RA11	2SK330		
2SJ661-E	2SK364	3 nF [C0805C302K1GACT U]	3.3 nF [C0402C332K8RACT U]
2SJ665-DL-E	2SK366		
2SK117	2SK367	3 nF [C0805C302K1HACT U]	3.3 nF [C0402C332K9RACT U]
2SK170	2SK368		
2SK192A	2SK3703	3 nF [C0805C302K3GACT U]	3.3 nF [C0603C332K1HACT U]
2SK208	2SK3704		
2SK209	2SK3746	3 nF [C0805C302K3HACT U]	3.3 nF [C0603C332K1RACT U]
2SK2553L	2SK3746-1E		
2SK2553S	2SK3747	3 nF [C0805C302K5HACT U]	3.3 nF [C0603C332K3GACT U]
2SK2978	2SK3747-1E		
2SK2980	2SK3748	3 nF [C1825C302KBGAC TU]	3.3 nF [C0603C332K3HACT U]
2SK3069	2SK3748-1E		
2SK3070L	2SK3820-DL-E	3 nF [C2220C302KBGAC TU]	3.3 nF [C0603C332K3RACT U]
2SK3070S	2SK3820-E		
2SK30ATM	2SWITCHCM	3 nF [C2225C302KBGAC TU]	3.3 nF [C0603C332K4RACT U]
2SK3133	2V7002LT1G		
2SK3134	2V7002LT3G	3 nF [C0603C302K1HACT U]	3.3 nF [C0402C332K3RACT U]
2SK3135	3 nF [C0603C302K1HACT U]	3.3 nF [C0402C332K4RACT U]	3.3 nF [C0603C332K5HACT U]
2SK3136			
2SK3140	3 nF [C0603C302K3HACT U]	3.3 nF [C0402C332K4RACT U]	3.3 nF [C0603C332K5RACT U]
2SK3141			
2SK3142			
2SK3203			

Multisim 14.0 Power Pro Components

3.3 nF [C0805C332K1GACT U]	3.3 nF [C0805C332K8GACT U]	3.3 nF [C1210C332K5RACT U]	3.3 uF [C1206C335K4RACT U]
3.3 nF [C0805C332K1HACT U]	3.3 nF [C0805C332KARACT U]	3.3 nF [C1825C332KBGAC TU]	3.3 uF [C1206C335K8PACT U]
3.3 nF [C0805C332K1RACT U]	3.3 nF [C1206C332K1GACT U]	3.3 nF [C2220C332KBGAC TU]	3.3 uF [C1206C335K8RACT U]
3.3 nF [C0805C332K2RACT U]	3.3 nF [C1206C332K1RACT U]	3.3 nF [C2225C332KBGAC TU]	3.3 uF [C1206C335K9PACT U]
3.3 nF [C0805C332K3GACT U]	3.3 nF [C1206C332K2RACT U]	3.3 nF [CA064C332K1RACT U]	3.3 uF [C1206C335K9RACT U]
3.3 nF [C0805C332K3HACT U]	3.3 nF [C1206C332K3RACT U]	3.3 nF [CA064C332K5RACT U]	3.3 uF [C1206C335M4VAC TU]
3.3 nF [C0805C332K4GACT U]	3.3 nF [C1206C332K5GACT U]	3.3 uF [C0805C335K4PACT U]	3.3 uF [C1206C335M9VAC TU]
3.3 nF [C0805C332K4RACT U]	3.3 nF [C1206C332K5RACT U]	3.3 uF [C0805C335K8PACT U]	3.3 uF [C1210C335K3PACT U]
3.3 nF [C0805C332K5GACT U]	3.3 nF [C1210C332K1RACT U]	3.3 uF [C0805C335K9PACT U]	3.3 uF [C1210C335K4PACT U]
3.3 nF [C0805C332K5HACT U]	3.3 nF [C1210C332K2GACT U]	3.3 uF [C1206C335K3PACT U]	3.3 uF [C1210C335K4RACT U]
3.3 nF [C0805C332K5RACT U]	3.3 nF [C1210C332K5GACT U]	3.3 uF [C1206C335K4PACT U]	3.3 uF [C1210C335K8PACT U]

Multisim 14.0 Power Pro Components

3.3 uF [T409B335M006AH 4250]	3.3 uF [T491D335M050AT]	3.3 uF [T494D335M050AT]	3.6 nF [C0603C362K3HACT U]
3.3 uF [T489A335M020AT E3K7]	3.3 uF [T491S335M010AT]	3.3 uF [T494S335M010AT]	3.6 nF [C0603C362K5HACT U]
3.3 uF [T491A335M004AT]	3.3 uF [T491T335M020AT]	3.3 uF [T494T335M020AT]	3.6 nF [C0805C362K1GACT U]
3.3 uF [T491A335M006AT]	3.3 uF [T493A335M004AH 6110]	3.3 uF [T495A335M016AT E3K0]	3.6 nF [C0805C362K1HACT U]
3.3 uF [T491A335M010AT]	3.3 uF [T494A335M004AT]	3.3 uF [T495B335M035AT E900]	3.6 nF [C0805C362K3HACT U]
3.3 uF [T491A335M016AT]	3.3 uF [T494A335M006AT]	3.3 uF [T495C335M035AT E525]	3.6 nF [C0805C362K5HACT U]
3.3 uF [T491A335M020AT]	3.3 uF [T494A335M010AT]	3.3 uF [T495C335M035AT E550]	3.6 nF [C1825C362KBGAC TU]
3.3 uF [T491B335M016AT]	3.3 uF [T494A335M016AT]	3.3 uF [T495C335M035AT E600]	3.6 nF [C2220C362KBGAC TU]
3.3 uF [T491B335M020AT]	3.3 uF [T494A335M020AT]	3.3 uF [T498A335M010AT E3K6]	3.6 nF [C2225C362KBGAC TU]
3.3 uF [T491B335M025AT]	3.3 uF [T494B335M016AT]	3.3 uF [T498A335M016AT E3K4]	3.9 nF [C0402C392K3RACT U]
3.3 uF [T491B335M035AT]	3.3 uF [T494B335M020AT]	3.3 uF [T498C335M035AT E1K7]	3.9 nF [C0402C392K4RACT U]
3.3 uF [T491C335M025AT]	3.3 uF [T494B335M025AT]	3.6 nF [C0603C362K1HACT U]	
3.3 uF [T491C335M035AT]	3.3 uF [T494C335M025AT]		
3.3 uF [T491D335M035AT]	3.3 uF [T494C335M035AT]		

Multisim 14.0 Power Pro Components

3.9 nF [C0402C392K5RACT U]	3.9 nF [C0805C392K1RACT U]	3.9 nF [C1206C392K1GACT U]	3.9 nF [CDR02BX392BKSM]
3.9 nF [C0603C392K1HACT U]	3.9 nF [C0805C392K2RACT U]	3.9 nF [C1206C392K1RACT U]	3.9 uF [C1206C395K4RACT U]
3.9 nF [C0603C392K1RACT U]	3.9 nF [C0805C392K3GACT U]	3.9 nF [C1206C392K2RACT U]	3.9 uF [C1206C395K8RACT U]
3.9 nF [C0603C392K3GACT U]	3.9 nF [C0805C392K3HACT U]	3.9 nF [C1206C392K5GACT U]	3.9 uF [C1206C395K9RACT U]
3.9 nF [C0603C392K3HACT U]	3.9 nF [C0805C392K3RACT U]	3.9 nF [C1206C392K5RACT U]	3.9 uF [C1210C395K3NAC TU]
3.9 nF [C0603C392K3RACT U]	3.9 nF [C0805C392K4GACT U]	3.9 nF [C1210C392K5RACT U]	3_AMP
3.9 nF [C0603C392K4RACT U]	3.9 nF [C0805C392K4RACT U]	3.9 nF [C1812C392K2GACT U]	30 mF [C0402C309K5GACT U]
3.9 nF [C0603C392K5HACT U]	3.9 nF [C0805C392K5GACT U]	3.9 nF [C1825C392KBGAC TU]	30 mF [C0805C309KBGAC TU]
3.9 nF [C0603C392K5RACT U]	3.9 nF [C0805C392K5HACT U]	3.9 nF [C2220C392KBGAC TU]	30 pF [C0402C300K5GACT U]
3.9 nF [C0805C392K1GACT U]	3.9 nF [C0805C392K5RACT U]	3.9 nF [C2225C392KBGAC TU]	30 pF [C0603C300K2GACT U]
3.9 nF [C0805C392K1HACT U]	3.9 nF [C0805C392KARACT U]	3.9 nF [C2225C392KCGAC TU]	30 pF [C0805C300K2GACT U]

Multisim 14.0 Power Pro Components

30 pF [C0805C300K5GACT U]	300 pF [C0402C301K3HACT U]	300 pF [C2225C301KBGAC TU]	33 nF [C0402C333K8PACT U]
30 pF [C0805C300KBGAC TU]	300 pF [C0402C301K5HACT U]	30CLJQ045 30CLJQ100	33 nF [C0402C333K8RACT U]
30 pF [C1206C300K1GACT U]	300 pF [C0805C301K1GACT U]	30CLJQ150 30LJQ045	33 nF [C0402C333K9PACT U]
30 pF [C1206C300K5GACT U]	300 pF [C0805C301K2GACT U]	30LJQ100 30LJQ150	33 nF [C0402C333K9RACT U]
30 pF [C1206C300KBGAC TU]	300 pF [C0805C301K5GACT U]	30SCLJQ030 30SCLJQ060	33 nF [C0603C333K1RACT U]
30 pF [C1210C300KBGAC TU]	300 pF [C1206C301K5GACT U]	30SLJQ030 30V_10W	33 nF [C0603C333K3RACT U]
30 pF [C1812C300KBGAC TU]	300 pF [C1206C301KBGAC TU]	3280A 3288RT	33 nF [C0603C333K4RACT U]
30 pF [C1825C300KBGAC TU]	300 pF [C1210C301KBGAC TU]	32CTQ030 33 mF	33 nF [C0603C333K5RACT U]
30 pF [C2220C300KBGAC TU]	300 pF [C1812C301KBGAC TU]	[C0805C339KBGAC TU] 33 mF	33 nF [C0603C333K8RACT U]
30 pF [C2225C300KBGAC TU]	300 pF [C1825C301KBGAC TU]	[C1206C339K5GACT U] 33 nF	33 nF [C0603C333M3VAC TU]
30_AMP 300 pF [C0402C301K1HACT U]	300 pF [C2220C301KBGAC TU]	[C0402C333K3RACT U] 33 nF	33 nF [C0805C333K1RACT U]

Multisim 14.0 Power Pro Components

33 nF [C0805C333K2RACT U]	33 nF [C0805F333K5RACT U]	33 nF [C1210C333K1GACT U]	33 nF [C1812C333K1HACT U]
33 nF [C0805C333K3GACT U]	33 nF [C1206C333K1HACT U]	33 nF [C1210C333K1HACT U]	33 nF [C1812C333K1RACT U]
33 nF [C0805C333K3HACT U]	33 nF [C1206C333K1RACT U]	33 nF [C1210C333K1RACT U]	33 nF [C1812C333K2RACT U]
33 nF [C0805C333K3RACT U]	33 nF [C1206C333K2RACT U]	33 nF [C1210C333K2RACT U]	33 nF [C1812C333K5GACT U]
33 nF [C0805C333K4RACT U]	33 nF [C1206C333K3GACT U]	33 nF [C1210C333K3GACT U]	33 nF [C1812C333K5HACT U]
33 nF [C0805C333K5RACT U]	33 nF [C1206C333K3HACT U]	33 nF [C1210C333K3HACT U]	33 nF [C1812C333K5RACT U]
33 nF [C0805C333K8RACT U]	33 nF [C1206C333K5HACT U]	33 nF [C1210C333K5GACT U]	33 nF [C1825C333K1RACT U]
33 nF [C0805C333M5UAC TU]	33 nF [C1206C333K5RACT U]	33 nF [C1210C333K5HACT U]	33 nF [C1825C333K5RACT U]
33 nF [C0805F333K1RACT U]	33 nF [C1206C333KARACT U]	33 nF [C1210C333K5RACT U]	33 nF [C2220C333K1GACT U]
33 nF [C0805F333K3RACT U]	33 nF [C1206C333M1UAC TU]	33 nF [C1210C333KARACT U]	33 nF [C2220C333K2GACT U]
33 nF [C0805F333K4RACT U]	33 nF [C1206C333M5UAC TU]	33 nF [C1812C333K1GACT U]	33 nF [C2220C333K5GACT U]

Multisim 14.0 Power Pro Components

33 nF [C2225C333K5GACT U]	33 pF [C0805C330K1GACT U]	33 pF [C1206C330KGGAC TU]	33 uF [A700V336M008AT E018]
33 nF [CA064C333K4RACT U]	33 pF [C0805C330K2GACT U]	33 pF [C1210C330KBGAC TU]	33 uF [A700V336M008AT E025]
33 pF [C0201C330K3GACT U]	33 pF [C0805C330K5GACT U]	33 pF [C1812C330KBGAC TU]	33 uF [A700V336M008AT E028]
33 pF [C0402C330K3GACT U]	33 pF [C0805C330KBGAC TU]	33 pF [C1825C330KBGAC TU]	33 uF [A700V336M010AT E018]
33 pF [C0402C330K4GACT U]	33 pF [C0805C330KDGAC TU]	33 pF [C2220C330KBGAC TU]	33 uF [A700V336M010AT E025]
33 pF [C0402C330K5GACT U]	33 pF [C1206C330K1GACT U]	33 pF [C2225C330KBGAC TU]	33 uF [A700V336M010AT E028]
33 pF [C0402C330K8GACT U]	33 pF [C1206C330K2GACT U]	33 pF [CA064C330K5GAC TU]	33 uF [T409F336M004AH 4250]
33 pF [C0603C330K1GACT U]	33 pF [C1206C330K5GACT U]	33 pF [CA064C330K8GAC TU]	33 uF [T409G336M010AH 4250]
33 pF [C0603C330K2GACT U]	33 pF [C1206C330KBGAC TU]	33 uF [A700V336M006AT E018]	33 uF [T419E336M006AH 4250]
33 pF [C0603C330K3GACT U]	33 pF [C1206C330KCGAC TU]	33 uF [A700V336M006AT E025]	33 uF [T419X336M025AH 4250]
33 pF [C0603C330K5GACT U]	33 pF [C1206C330KDGAC TU]	33 uF [A700V336M006AT E028]	33 uF [T489D336M020AT E250]

Multisim 14.0 Power Pro Components

33 uF [T491A336M003AT]	33 uF [T491D336M016AT]	33 uF [T491V336M020AT]	33 uF [T494C336M025AT]
33 uF [T491A336M004AT]	33 uF [T491D336M020AT]	33 uF [T491X336M025AT]	33 uF [T494D336M010AT]
33 uF [T491A336M006AT]	33 uF [T491D336M025AT]	33 uF [T491X336M035AT]	33 uF [T494D336M016AT]
33 uF [T491A336M010AT]	33 uF [T491D336M035AT]	33 uF [T494A336M003AT]	33 uF [T494D336M020AT]
33 uF [T491B336M004AT]	33 uF [T491D336M004AT]	33 uF [T494A336M004AT]	33 uF [T494D336M025AT]
33 uF [T491B336M006AT]	33 uF [T491T336M004AT]	33 uF [T494A336M006AT]	33 uF [T494D336M035AT]
33 uF [T491B336M010AT]	33 uF [T491T336M006AT]	33 uF [T494A336M010AT]	33 uF [T494T336M004AT]
33 uF [T491B336M016AT]	33 uF [T491T336M010AT]	33 uF [T494B336M004AT]	33 uF [T494T336M006AT]
33 uF [T491C336M004AT]	33 uF [T491U336M004AT]	33 uF [T494B336M010AT]	33 uF [T494T336M010AT]
33 uF [T491C336M006AT]	33 uF [T491U336M006AT]	33 uF [T494C336M004AT]	33 uF [T494U336M004AT]
33 uF [T491C336M010AT]	33 uF [T491U336M010AT]	33 uF [T494C336M006AT]	33 uF [T494U336M006AT]
33 uF [T491C336M016AT]	33 uF [T491U336M016AT]	33 uF [T494C336M010AT]	33 uF [T494U336M010AT]
33 uF [T491C336M020AT]	33 uF [T491V336M010AT]	33 uF [T494C336M016AT]	33 uF [T494U336M020AT]
33 uF [T491D336M010AT]			

Multisim 14.0 Power Pro Components

33 uF [T494U336M016AT]	33 uF [T495D336M025AT E100]	33 uF [T495X336M035AT E250]	33 uF [T520A336M006AT E080]
33 uF [T494V336M010AT]	33 uF [T495D336M025AT E225]	33 uF [T497H336M015AT 6110]	33 uF [T520B336M006AT E025]
33 uF [T494V336M020AT]	33 uF [T495D336M025AT E300]	33 uF [T498B336M006AT E1K7]	33 uF [T520B336M006AT E035]
33 uF [T494X336M025AT]	33 uF [T495E336M035AT E200]	33 uF [T498D336M016AT E600]	33 uF [T520B336M006AT E040]
33 uF [T495B336M010AT E450]	33 uF [T495V336M010AT E100]	33 uF [T498D336M025AT E600]	33 uF [T520B336M006AT E070]
33 uF [T495C336M016AT E200]	33 uF [T495V336M010AT E150]	33 uF [T498X336M035AT E500]	33 uF [T520B336M008AT E025]
33 uF [T495C336M016AT E275]	33 uF [T495X336M025AT E100]	33 uF [T510X336M035AT E050]	33 uF [T520B336M008AT E035]
33 uF [T495D336M016AT E225]	33 uF [T495X336M025AT E175]	33 uF [T510X336M035AT E065]	33 uF [T520B336M008AT E040]
33 uF [T495D336M020AT E100]	33 uF [T495X336M025AT E200]	33 uF [T520A336M004AT E070]	33 uF [T520B336M008AT E070]
33 uF [T495D336M020AT E200]	33 uF [T495X336M035AT E100]	33 uF [T520A336M004AT E080]	33 uF [T520B336M010AT E035]
33 uF [T495D336M025AT E090]	33 uF [T495X336M035AT E175]	33 uF [T520A336M006AT E070]	33 uF [T520B336M010AT E040]

Multisim 14.0 Power Pro Components

33 uF [T520B336M010AT E070]	33 uF [T520V336M016AT E070]	33 uF [T543A336M004AT E070]	330 nF [C0805C334M3VAC TU]
33 uF [T520C336M006AT E100]	33 uF [T520W336M016AT E045]	33 uF [T543B336M010AT E040]	330 nF [C0805C334M4VAC TU]
33 uF [T520T336M006AT E070]	33 uF [T521D336M025AT E060]	330 nF [C0603C334K4PACT U]	330 nF [C0805C334M8VAC TU]
33 uF [T520T336M008AT E070]	33 uF [T521D336M035AT E065]	330 nF [C0603C334K4RACT U]	330 nF [C1206C334K1RACT U]
33 uF [T520T336M008AT E080]	33 uF [T521V336M025AT E060]	330 nF [C0603C334K8PACT U]	330 nF [C1206C334K3RACT U]
33 uF [T520T336M010AT E070]	33 uF [T525B336M006AT E080]	330 nF [C0603C334K8RACT U]	330 nF [C1206C334K4RACT U]
33 uF [T520T336M010AT E080]	33 uF [T525B336M010AT E080]	330 nF [C0603C334K9RACT U]	330 nF [C1206C334K5RACT U]
33 uF [T520U336M008AT E070]	33 uF [T525T336M008AT E080]	330 nF [C0805C334K3NAC TU]	330 nF [C1206C334M3VAC TU]
33 uF [T520U336M010AT E070]	33 uF [T525T336M010AT E080]	330 nF [C0805C334K3RACT U]	330 nF [C1206F334K3RACT U]
33 uF [T520V336M016AT E045]	33 uF [T528I336M010ATE 150]	330 nF [C0805C334K4RACT U]	330 nF [C1206F334K4RACT U]
33 uF [T520V336M016AT E060]	33 uF [T541X336M050AH 6510]	330 nF [C0805C334K8RACT U]	330 nF [C1210C334K1RACT U]

Multisim 14.0 Power Pro Components

330 nF [C1210C334K3RACT U]	330 nF [C1812C334M5UAC TU]	330 nF [C2220C334K2RACT U]	330 nF [T494A334M035AT]
330 nF [C1210C334K5RACT U]	330 nF [C1812F334K1RACT U]	330 nF [C2220C334K5GACT U]	330 nF [T494B334M050AT]
330 nF [C1210C334M5UAC TU]	330 nF [C1812F334K2RACT U]	330 nF [C2220C334K5RACT U]	330 nF [T496B334M050AT 6110]
330 nF [C1210C334M5VAC TU]	330 nF [C1812F334K3RACT U]	330 nF [C2225C334K1RACT U]	330 pF [C0402C331K1HACT U]
330 nF [C1210F334K1RACT U]	330 nF [C1812F334K5RACT U]	330 nF [C2225C334K2RACT U]	330 pF [C0402C331K3HACT U]
330 nF [C1210F334K3RACT U]	330 nF [C1825C334K1RACT U]	330 nF [C2225C334K5RACT U]	330 pF [C0402C331K4GACT U]
330 nF [C1210F334K4RACT U]	330 nF [C1825C334K2RACT U]	330 nF [C2225C334M5UAC TU]	330 pF [C0402C331K4RACT U]
330 nF [C1210F334K5RACT U]	330 nF [C1825C334K5RACT U]	330 nF [T409A334M025AH 4250]	330 pF [C0402C331K5GACT U]
330 nF [C1812C334K1RACT U]	330 nF [C1825C334M5UAC TU]	330 nF [T491A334M025AT]	330 pF [C0402C331K5HACT U]
330 nF [C1812C334K5RACT U]	330 nF [C2220C334K1GACT U]	330 nF [T491B334M050AT]	330 pF [C0402C331K5RACT U]
330 nF [C1812C334KARACT U]	330 nF [C2220C334K1RACT U]	330 nF [T494A334M025AT]	330 pF [C0402C331K8RACT U]

Multisim 14.0 Power Pro Components

330 pF [C0603C331K1RACT U]	330 pF [C0805C331K2RACT U]	330 pF [C1206C331KCGAC TU]	330 uF [A700X337M002AT E010]
330 pF [C0603C331K2RACT U]	330 pF [C0805C331K3GACT U]	330 pF [C1210C331K1GACT U]	330 uF [A700X337M002AT E015]
330 pF [C0603C331K3GACT U]	330 pF [C0805C331K3RACT U]	330 pF [C1210C331K5GACT U]	330 uF [A700X337M004AT E010]
330 pF [C0603C331K3RACT U]	330 pF [C0805C331K4RACT U]	330 pF [C1210C331KBGAC TU]	330 uF [A700X337M004AT E015]
330 pF [C0603C331K4RACT U]	330 pF [C0805C331K5GACT U]	330 pF [C1812C331KBGAC TU]	330 uF [A700X337M2R5AT E010]
330 pF [C0603C331K5GACT U]	330 pF [C0805C331K5RACT U]	330 pF [C1825C331KBGAC TU]	330 uF [A700X337M2R5AT E015]
330 pF [C0603C331K5RACT U]	330 pF [C0805C331K8RACT U]	330 pF [C2220C331KBGAC TU]	330 uF [T489X337M010AT E100]
330 pF [C0603C331K8RACT U]	330 pF [C1206C331K1GACT U]	330 pF [C2225C331KBGAC TU]	330 uF [T491C337M004AT]
330 pF [C0805C331K1GACT U]	330 pF [C1206C331K2GACT U]	330 pF [CA064C331K5GAC TU]	330 uF [T491D337M004AT]
330 pF [C0805C331K1RACT U]	330 pF [C1206C331K5GACT U]	330 pF [CA064C331K5RACT U]	330 uF [T491D337M006AT]
330 pF [C0805C331K2GACT U]	330 pF [C1206C331KBGAC TU]	330 uF [A700D337M002AT E007]	330 uF [T491D337M010AT]
			330 uF [T491E337M006AT]

Multisim 14.0 Power Pro Components

330 uF [T491E337M010AT]	330 uF [T495D337M006AT E040]	330 uF [T495X337M010AT E035]	330 uF [T520C337M2R5AT E045]
330 uF [T491V337M004AT]	330 uF [T495D337M006AT E050]	330 uF [T495X337M010AT E050]	330 uF [T520D337M004AT E006]
330 uF [T491X337M006AT]	330 uF [T495D337M006AT E070]	330 uF [T495X337M010AT E060]	330 uF [T520D337M004AT E007]
330 uF [T494C337M004AT]	330 uF [T495D337M006AT E100]	330 uF [T495X337M010AT E100]	330 uF [T520D337M004AT E009]
330 uF [T494D337M004AT]	330 uF [T495D337M010AT E100]	330 uF [T510X337M010AT E035]	330 uF [T520D337M004AT E012]
330 uF [T494D337M006AT]	330 uF [T495D337M010AT E125]	330 uF [T513X337M010AH 6110]	330 uF [T520D337M004AT E015]
330 uF [T494D337M010AT]	330 uF [T495D337M010AT E150]	330 uF [T520B337M2R5AT E045]	330 uF [T520D337M004AT E040]
330 uF [T494E337M006AT]	330 uF [T495E337M010AT E060]	330 uF [T520B337M2R5AT E070]	330 uF [T520D337M004AT E045]
330 uF [T494V337M004AT]	330 uF [T495X337M006AT E045]	330 uF [T520C337M004AT E025]	330 uF [T520D337M006AT E009]
330 uF [T494X337M006AT]	330 uF [T495X337M006AT E065]	330 uF [T520C337M2R5AT E015]	330 uF [T520D337M006AT E010]
330 uF [T494X337M010AT]	330 uF [T495X337M006AT E100]	330 uF [T520C337M2R5AT E025]	330 uF [T520D337M006AT E015]
330 uF [T495D337M004AT E030]			

Multisim 14.0 Power Pro Components

330 uF [T520D337M006AT E025]	330 uF [T520V337M003AT E025]	330 uF [T520V337M2R5AT E007]	330 uF [T520X337M010AT E040]
330 uF [T520D337M006AT E040]	330 uF [T520V337M004AT E007]	330 uF [T520V337M2R5AT E009]	330 uF [T520Y337M006AT E015]
330 uF [T520D337M006AT E045]	330 uF [T520V337M004AT E009]	330 uF [T520V337M2R5AT E012]	330 uF [T520Y337M006AT E025]
330 uF [T520D337M2R5AT E006]	330 uF [T520V337M004AT E012]	330 uF [T520V337M2R5AT E015]	330 uF [T520Y337M006AT E040]
330 uF [T520D337M2R5AT E007]	330 uF [T520V337M004AT E018]	330 uF [T520V337M2R5AT E018]	330 uF [T520Y337M010AT E015]
330 uF [T520L337M2R5AT E009]	330 uF [T520V337M004AT E025]	330 uF [T520V337M2R5AT E025]	330 uF [T520Y337M010AT E035]
330 uF [T520L337M2R5AT E012]	330 uF [T520V337M004AT E040]	330 uF [T520V337M2R5AT E040]	330 uF [T522V337M006AT E040]
330 uF [T520L337M2R5AT E025]	330 uF [T520V337M006AT E015]	330 uF [T520W337M2R5A TE025]	330 uF [T525D337M003AT E025]
330 uF [T520V337M003AT E009]	330 uF [T520V337M006AT E025]	330 uF [T520W337M2R5A TE040]	330 uF [T525D337M004AT E025]
330 uF [T520V337M003AT E012]	330 uF [T520V337M006AT E040]	330 uF [T520X337M010AT E010]	330 uF [T525D337M006AT E025]
330 uF [T520V337M003AT E015]	330 uF [T520V337M2R5AT E006]	330 uF [T520X337M010AT E025]	330 uF [T525D337M006AT E040]

Multisim 14.0 Power Pro Components

330 uF [T525D337M2R5AT E025]	330 uF [T530X337M010AT E004]	3554SM 35CGQ045	36 pF [C2220C360KBGAC TU]
330 uF [T528Z337M004AT E009]	330 uF [T530X337M010AT E005]	35CGQ100 35CGQ150	36 pF [C2220C360KZGACT U]
330 uF [T528Z337M004AT E012]	330 uF [T530X337M010AT E006]	35CLQ045 35GQ100	36 pF [C2225C360KBGAC TU]
330 uF [T528Z337M2R5AT E005]	330 uF [T530X337M010AT E010]	35GQ150 35SCGQ030	360 pF [C0402C361K1HACT U]
330 uF [T528Z337M2R5AT E007]	330 uF [T530Y337M006AT E006]	35SCGQ060 35SGQ060	360 pF [C0402C361K3HACT U]
330 uF [T528Z337M2R5AT E008]	330 uF [T541X337M010AH 6520]	36 mF [C0805C369KBGAC TU]	360 pF [C0402C361K5HACT U]
330 uF [T528Z337M2R5AT E009]	330 uF [T541Y337M006AH 6510]	36 pF [C0805C360KBGAC TU]	360 pF [C0603C361K5GACT U]
330 uF [T528Z337M2R5AT E012]	330 uF [T543C337M2R5AT E045]	36 pF [C1206C360KBGAC TU]	360 pF [C1206C361KBGAC TU]
330 uF [T530D337M004AT E006]	330 uF [T543L337M2R5AT E025]	36 pF [C1210C360KBGAC TU]	360 pF [C1210C361KBGAC TU]
330 uF [T530D337M006AT E006]	330 uF [T543Y337M006AT E015]	36 pF [C1812C360KBGAC TU]	360 pF [C1812C361KBGAC TU]
330 uF [T530D337M006AT E010]	3-534206-0 3554AM 3554BM	36 pF [C1825C360KBGAC TU]	360 pF [C1825C361KBGAC TU]

Multisim 14.0 Power Pro Components

360 pF [C2220C361KBGAC TU]	39 nF [C0603C393K8RACT U]	39 nF [C1206C393K4RACT U]	39 pF [C0201C390K3GACT U]
360 pF [C2225C361KBGAC TU]	39 nF [C0805C393K1RACT U]	39 nF [C1206C393K5RACT U]	39 pF [C0402C390K4GACT U]
3-644456-5 3-644456-8	39 nF [C0805C393K3RACT U]	39 nF [C1206C393KARACT U]	39 pF [C0402C390K5GACT U]
39 mF [C0805C399KBGAC TU]	39 nF [C0805C393K4RACT U]	39 nF [C1206C393M1UAC TU]	39 pF [C0402C390K8GACT U]
39 nF [C0402C393K4RACT U]	39 nF [C0805C393K5RACT U]	39 nF [C1210C393K1RACT U]	39 pF [C0603C390K2GACT U]
39 nF [C0402C393K8RACT U]	39 nF [C0805C393K8RACT U]	39 nF [C1210C393K2RACT U]	39 pF [C0603C390K5GACT U]
39 nF [C0402C393K9RACT U]	39 nF [C0805F393K1RACT U]	39 nF [C1210C393K5RACT U]	39 pF [C0805C390K1GACT U]
39 nF [C0603C393K1RACT U]	39 nF [C0805F393K3RACT U]	39 nF [C1210C393KARACT U]	39 pF [C0805C390K2GACT U]
39 nF [C0603C393K3RACT U]	39 nF [C0805F393K4RACT U]	39 nF [C1812C393K1RACT U]	39 pF [C0805C390K5GACT U]
39 nF [C0603C393K4RACT U]	39 nF [C0805F393K5RACT U]	39 nF [C1812C393K5RACT U]	39 pF [C0805C390KBGAC TU]
39 nF [C0603C393K5RACT U]	39 nF [C1206C393K1RACT U]	39 nF [C2220C393K2GACT U]	39 pF [C0805C390KCGAC TU]

Multisim 14.0 Power Pro Components

39 pF [C1206C390K1GACT U]	390 nF [C0603C394K4RACT U]	390 nF [C1206C394K5RACT U]	390 nF [C1812C394KARACT U]
39 pF [C1206C390K2GACT U]	390 nF [C0603C394K8PACT U]	390 nF [C1206C394K8RACT U]	390 nF [C1812C394M5UAC TU]
39 pF [C1206C390K5GACT U]	390 nF [C0603C394K8RACT U]	390 nF [C1206F394K3RACT U]	390 nF [C1812F394K1RACT U]
39 pF [C1206C390KBGAC TU]	390 nF [C0603C394K9RACT U]	390 nF [C1206F394K4RACT U]	390 nF [C1812F394K2RACT U]
39 pF [C1210C390KBGAC TU]	390 nF [C0805C394K3RACT U]	390 nF [C1210C394K3RACT U]	390 nF [C1812F394K3RACT U]
39 pF [C1812C390KBGAC TU]	390 nF [C0805C394K4RACT U]	390 nF [C1210C394K5RACT U]	390 nF [C1812F394K5RACT U]
39 pF [C1825C390KBGAC TU]	390 nF [C0805C394K8RACT U]	390 nF [C1210F394K3RACT U]	390 nF [C1825C394K1RACT U]
39 pF [C2220C390KBGAC TU]	390 nF [C0805C394K9RACT U]	390 nF [C1210F394K4RACT U]	390 nF [C1825C394K2RACT U]
39 pF [C2225C390KBGAC TU]	390 nF [C1206C394K1RACT U]	390 nF [C1210F394K5RACT U]	390 nF [C1825C394K5RACT U]
39 pF [CA064C390K5GAC TU]	390 nF [C1206C394K3RACT U]	390 nF [C1812C394K1RACT U]	390 nF [C2225C394K1RACT U]
390 nF [C0603C394K4PACT U]	390 nF [C1206C394K4RACT U]	390 nF [C1812C394K5RACT U]	390 nF [C2225C394K2RACT U]

Multisim 14.0 Power Pro Components

390 pF [C0402C391K1HACT U]	390 pF [C0603C391K5GACT U]	390 pF [C1206C391KBGAC TU]	3KASMC15AHE3/57 T
390 pF [C0402C391K3HACT U]	390 pF [C0603C391K5RACT U]	390 pF [C1206C391KCGAC TU]	3KASMC24AHE3/9A T
390 pF [C0402C391K3RACT U]	390 pF [C0805C391K1GACT U]	390 pF [C1210C391KBGAC TU]	3KASMC28AHM3/5 7T
390 pF [C0402C391K4RACT U]	390 pF [C0805C391K1RACT U]	390 pF [C1812C391KBGAC TU]	3Line_Bussed
390 pF [C0402C391K5HACT U]	390 pF [C0805C391K2GACT U]	390 pF [C1825C391KBGAC TU]	3Line_Isolated
390 pF [C0402C391K5RACT U]	390 pF [C0805C391K4RACT U]	390 pF [C2220C391KBGAC TU]	3LN01M-TL-E
390 pF [C0603C391K1RACT U]	390 pF [C0805C391K5GACT U]	390 pF [C2225C391KBGAC TU]	3LN01M-TL-H
390 pF [C0603C391K2RACT U]	390 pF [C0805C391K5RACT U]	390 pF [CA064C391K5GAC TU]	3LN01SS-TL-E
390 pF [C0603C391K3GACT U]	390 pF [C1206C391K1GACT U]	390 uF [A700X397M002AT E010]	3LN01SS-TL-H
390 pF [C0603C391K3RACT U]	390 pF [C1206C391K2GACT U]	390 uF [A700X397M002AT E015]	3LP01SS-TL-E
390 pF [C0603C391K4RACT U]	390 pF [C1206C391K5GACT U]	3BH41	3LP01SS-TL-H
		3GH41	3LP01S-TL-E
		3JH41	3N246

Multisim 14.0 Power Pro Components

3N257	4.3 nF [C0805C432K5HACT U]	4.7 nF [C0603C472K3GACT U]	4.7 nF [C0805C472K2RACT U]
3N258			
3N259	4.3 nF [C1825C432KBGAC TU]	4.7 nF [C0603C472K3HACT U]	4.7 nF [C0805C472K3GACT U]
3P1S			
3P2S	4.3 nF [C2220C432KBGAC TU]	4.7 nF [C0603C472K3RACT U]	4.7 nF [C0805C472K3HACT U]
3P3S			
3P4S	4.3 nF [C2225C432KBGAC TU]	4.7 nF [C0603C472K4RACT U]	4.7 nF [C0805C472K3RACT U]
3P5S			
3PDT_DB	4.7 nF [C0402C472K3RACT U]	4.7 nF [C0603C472K5HACT U]	4.7 nF [C0805C472K4RACT U]
3PDT_SB			
3PST_DB	4.7 nF [C0402C472K4RACT U]	4.7 nF [C0603C472K5RACT U]	4.7 nF [C0805C472K5HACT U]
3PST_SB			
4.3 nF [C0603C432K1HACT U]	4.7 nF [C0402C472K5RACT U]	4.7 nF [C0603C472K8RACT U]	4.7 nF [C0805C472K5RACT U]
4.3 nF [C0603C432K3HACT U]	4.7 nF [C0402C472K8RACT U]	4.7 nF [C0603C472K9RACT U]	4.7 nF [C0805C472KARACT U]
4.3 nF [C0603C432K5HACT U]	4.7 nF [C0402C472K9RACT U]	4.7 nF [C0805C472K1GACT U]	4.7 nF [C1206C472K1RACT U]
4.3 nF [C0805C432K1GACT U]	4.7 nF [C0603C472K1HACT U]	4.7 nF [C0805C472K1HACT U]	4.7 nF [C1206C472K2RACT U]
4.3 nF [C0805C432K1HACT U]	4.7 nF [C0603C472K1RACT U]	4.7 nF [C0805C472K1RACT U]	4.7 nF [C1206C472K3RACT U]

Multisim 14.0 Power Pro Components

4.7 nF [C1206C472K4GACT U]	4.7 nF [C1825C472K2GACT U]	4.7 uF [C0805C475K8PACT U]	4.7 uF [C1206C475K9RACT U]
4.7 nF [C1206C472K5GACT U]	4.7 nF [C1825C472KBGAC TU]	4.7 uF [C0805C475K9PACT U]	4.7 uF [C1210C475K3NAC TU]
4.7 nF [C1206C472K5RACT U]	4.7 nF [C2220C472KBGAC TU]	4.7 uF [C1206C475K3PACT U]	4.7 uF [C1210C475K3PACT U]
4.7 nF [C1210C472K1GACT U]	4.7 nF [C2225C472K2GACT U]	4.7 uF [C1206C475K3RACT U]	4.7 uF [C1210C475K3RACT U]
4.7 nF [C1210C472K1RACT U]	4.7 nF [C2225C472KBGAC TU]	4.7 uF [C1206C475K4PACT U]	4.7 uF [C1210C475K4PACT U]
4.7 nF [C1210C472K2RACT U]	4.7 nF [CA064C472K3RACT U]	4.7 uF [C1206C475K4RACT U]	4.7 uF [C1210C475K4RACT U]
4.7 nF [C1210C472K5GACT U]	4.7 nF [CA064C472K5RACT U]	4.7 uF [C1206C475K5PACT U]	4.7 uF [C1210C475K5R1C7 186]
4.7 nF [C1210C472K5RACT U]	4.7 uF [C0603C475K8PACT U]	4.7 uF [C1206C475K8NAC TU]	4.7 uF [C1210C475K5RACT U]
4.7 nF [C1812C472K1GACT U]	4.7 uF [C0603C475K9PACT U]	4.7 uF [C1206C475K8PACT U]	4.7 uF [C1210C475K8PACT U]
4.7 nF [C1812C472K2GACT U]	4.7 uF [C0805C475K3PACT U]	4.7 uF [C1206C475K8RACT U]	4.7 uF [C1210C475K8RACT U]
4.7 nF [C1812C472K5GACT U]	4.7 uF [C0805C475K4PACT U]	4.7 uF [C1206C475K9PACT U]	4.7 uF [C1210C475K9PACT U]

Multisim 14.0 Power Pro Components

4.7 uF [C1210C475K9RACT U]	4.7 uF [T491B475M020AT]	4.7 uF [T494A475M025AT]	4.7 uF [T495B475M016AT E700]
4.7 uF [C1210C475M4VAC TU]	4.7 uF [T491B475M025AT]	4.7 uF [T494B475M010AT]	4.7 uF [T495C475M035AT E450]
4.7 uF [C1210C475M8VAC TU]	4.7 uF [T491C475M020AT]	4.7 uF [T494B475M016AT]	4.7 uF [T495C475M035AT E500]
4.7 uF [T409D475M010AH 4250]	4.7 uF [T491C475M035AT]	4.7 uF [T494B475M025AT]	4.7 uF [T495C475M035AT E600]
4.7 uF [T429C475M006AH 4250]	4.7 uF [T491D475M035AT]	4.7 uF [T494C475M020AT]	4.7 uF [T495D475M050AT E275]
4.7 uF [T491A475M004AT]	4.7 uF [T491D475M050AT]	4.7 uF [T494C475M035AT]	4.7 uF [T495D475M050AT E300]
4.7 uF [T491A475M006AT]	4.7 uF [T491S475M006AT]	4.7 uF [T494D475M035AT]	4.7 uF [T495X475M050AT E300]
4.7 uF [T491A475M010AT]	4.7 uF [T491S475M010AT]	4.7 uF [T494D475M050AT]	4.7 uF [T498A475M010AT E2K9]
4.7 uF [T491A475M016AT]	4.7 uF [T491T475M016AT]	4.7 uF [T494S475M006AT]	4.7 uF [T498B475M010AT E2K7]
4.7 uF [T491A475M020AT]	4.7 uF [T494A475M004AT]	4.7 uF [T494S475M010AT]	4.7 uF [T498B475M016AT E2K1]
4.7 uF [T491A475M025AT]	4.7 uF [T494A475M010AT]	4.7 uF [T494T475M016AT]	4.7 uF [T521D475M063AT E075]
4.7 uF [T491B475M010AT]	4.7 uF [T494A475M016AT]	4.7 uF [T495A475M010AT E1K3]	
	4.7 uF [T494A475M020AT]		

Multisim 14.0 Power Pro Components

4.7 uF [T521D475M063AT E300]	4001BT_15V	4009BCP_10V	4010BF_5V
	4001BT_5V	4009BCP_15V	4010BF_5V
4.7 uF [T540D475M063AH 6510]	4002BD_10V	4009BCP_5V	4010BM1_10V
	4002BD_15V	4009BCP_5V	4010BM1_15V
	4002BD_5V	4009BD_10V	4010BM1_5V
4_AMP	4002BP_10V	4009BD_15V	4011BD_10V
40_AMP	4002BP_15V	4009BD_5V	4011BD_15V
4000BD_10V	4002BP_5V	40106BD_10V	4011BD_5V
4000BD_15V	4002BP_5V	40106BD_15V	4011BP_10V
4000BD_5V	4002BT_10V	40106BD_5V	4011BP_15V
4000BP_10V	4002BT_15V	40106BP_10V	4011BP_5V
4000BP_15V	4002BT_5V	40106BP_15V	4011BP_5V
4000BP_5V	4008BD_10V	40106BP_5V	4011BT_10V
4000BP_5V	4008BD_15V	40106BP_5V	4011BT_15V
4000BT_10V	4008BD_5V	40106BT_10V	4011BT_5V
4000BT_15V	4008BP_10V	40106BT_15V	4012BD_10V
4000BT_5V	4008BP_15V	40106BT_5V	4012BD_15V
4001BD_10V	4008BP_5V	4010BC1_10V	4012BD_5V
4001BD_15V	4008BP_5V	4010BC1_15V	4012BP_10V
4001BD_5V	4008BT_10V	4010BC1_5V	4012BP_15V
4001BP_10V	4008BT_15V	4010BEY_10V	4012BP_5V
4001BP_15V	4008BT_5V	4010BEY_15V	4012BP_5V
4001BP_5V	4009BCL_10V	4010BEY_5V	4012BT_10V
4001BP_5V	4009BCL_15V	4010BF_10V	4012BT_15V
4001BT_10V	4009BCL_5V	4010BF_15V	4012BT_5V

Multisim 14.0 Power Pro Components

4013BD_10V	4015BP_5V	40162BD_5V	40175BD_10V
4013BD_15V	4015BP_5V	40162BP_10V	40175BD_15V
4013BD_5V	4015BT_10V	40162BP_15V	40175BD_5V
4013BP_10V	4015BT_15V	40162BP_5V	40175BP_10V
4013BP_15V	4015BT_5V	40162BT_10V	40175BP_15V
4013BP_5V	40160BD_10V	40162BT_15V	40175BP_5V
4013BP_5V	40160BD_15V	40162BT_5V	40175BT_10V
4013BT_10V	40160BD_5V	40163BD_10V	40175BT_15V
4013BT_15V	40160BP_10V	40163BD_15V	40175BT_5V
4013BT_5V	40160BP_15V	40163BD_5V	4017BD_10V
4014BD_10V	40160BP_5V	40163BP_10V	4017BD_15V
4014BD_15V	40160BT_10V	40163BP_15V	4017BD_5V
4014BD_5V	40160BT_15V	40163BP_5V	4017BP_10V
4014BP_10V	40160BT_5V	40163BT_10V	4017BP_10V
4014BP_15V	40161BD_10V	40163BT_15V	4017BP_15V
4014BP_5V	40161BD_15V	40163BT_5V	4017BP_5V
4014BP_5V	40161BD_5V	40174BD_10V	4017BP_5V
4014BT_10V	40161BP_10V	40174BD_15V	4017BT_10V
4014BT_15V	40161BP_15V	40174BD_5V	4017BT_15V
4014BT_5V	40161BP_5V	40174BP_10V	4017BT_5V
4015BD_10V	40161BT_10V	40174BP_15V	4018BD_10V
4015BD_15V	40161BT_15V	40174BP_5V	4018BD_15V
4015BD_5V	40161BT_5V	40174BT_10V	4018BD_5V
4015BP_10V	40162BD_10V	40174BT_15V	4018BP_10V
4015BP_15V	40162BD_15V	40174BT_5V	4018BP_15V

Multisim 14.0 Power Pro Components

4018BP_5V	40194BP_10V	4020BD_10V	4023BP_5V
4018BT_10V	40194BP_15V	4020BD_15V	4023BT_10V
4018BT_15V	40194BP_5V	4020BD_5V	4023BT_15V
4018BT_5V	40194BT_10V	4020BP_10V	4023BT_5V
40192BD_10V	40194BT_15V	4020BP_10V	40240BP_10V
40192BD_15V	40194BT_5V	4020BP_15V	40240BP_15V
40192BD_5V	40195BD_10V	4020BP_5V	40240BP_5V
40192BP_10V	40195BD_15V	4020BT_10V	40240BT_10V
40192BP_15V	40195BD_5V	4020BT_15V	40240BT_15V
40192BP_5V	40195BP_10V	4020BT_5V	40240BT_5V
40192BT_10V	40195BP_15V	4021BD_10V	40244BP_10V
40192BT_15V	40195BP_5V	4021BD_15V	40244BP_15V
40192BT_5V	40195BT_10V	4021BD_5V	40244BP_5V
40193BD_10V	40195BT_15V	4021BP_10V	40244BT_10V
40193BD_15V	40195BT_5V	4021BP_15V	40244BT_15V
40193BD_5V	4019BD_10V	4021BP_5V	40244BT_5V
40193BP_10V	4019BD_15V	4021BT_10V	40245BP_10V
40193BP_15V	4019BD_5V	4021BT_15V	40245BP_15V
40193BP_5V	4019BP_10V	4021BT_5V	40245BP_5V
40193BT_10V	4019BP_15V	4023BD_10V	40245BT_10V
40193BT_15V	4019BP_5V	4023BD_15V	40245BT_15V
40193BT_5V	4019BP_5V	4023BD_5V	40245BT_5V
40194BD_10V	4019BT_10V	4023BP_10V	4024BD_10V
40194BD_15V	4019BT_15V	4023BP_15V	4024BD_15V
40194BD_5V	4019BT_5V	4023BP_5V	4024BD_5V

Multisim 14.0 Power Pro Components

4024BP_10V	4027BT_15V	4030BP_15V	40373BP_15V
4024BP_15V	4027BT_5V	4030BP_5V	40373BP_5V
4024BP_5V	4028BD_10V	4030BP_5V	40373BT_10V
4024BP_5V	4028BD_15V	4030BT_10V	40373BT_15V
4024BT_10V	4028BD_5V	4030BT_15V	40373BT_5V
4024BT_15V	4028BP_10V	4030BT_5V	40374BP_10V
4024BT_5V	4028BP_15V	4032BCL_10V	40374BP_15V
4025BD_10V	4028BP_5V	4032BCL_15V	40374BP_5V
4025BD_15V	4028BP_5V	4032BCL_5V	40374BT_10V
4025BD_5V	4028BT_10V	4032BCP_10V	40374BT_15V
4025BP_10V	4028BT_15V	4032BCP_15V	40374BT_5V
4025BP_15V	4028BT_5V	4032BCP_5V	4038BCL_10V
4025BP_5V	4029BD_10V	4032BD_10V	4038BCL_15V
4025BP_5V	4029BD_15V	4032BD_15V	4038BCL_5V
4025BT_10V	4029BD_5V	4032BD_5V	4038BCP_10V
4025BT_15V	4029BP_10V	4035BD_10V	4038BCP_15V
4025BT_5V	4029BP_15V	4035BD_15V	4038BCP_5V
4027BD_10V	4029BP_5V	4035BD_5V	4038BD_10V
4027BD_15V	4029BT_10V	4035BP_10V	4038BD_15V
4027BD_5V	4029BT_15V	4035BP_15V	4038BD_5V
4027BP_10V	4029BT_5V	4035BP_5V	4040BD_10V
4027BP_15V	4030BD_10V	4035BT_10V	4040BD_15V
4027BP_5V	4030BD_15V	4035BT_15V	4040BD_5V
4027BP_5V	4030BD_5V	4035BT_5V	4040BP_10V
4027BT_10V	4030BP_10V	40373BP_10V	4040BP_15V

Multisim 14.0 Power Pro Components

4040BP_5V	4043BD_10V	4049BP_5V	4066BD_15V
4040BP_5V	4043BD_15V	4049BP_5V	4066BD_5V
4040BT_10V	4043BD_5V	4049BT_10V	4066BP_10V
4040BT_15V	4043BP_10V	4049BT_15V	4066BP_15V
4040BT_5V	4043BP_15V	4049BT_5V	4066BP_5V
4041BD_10V	4043BP_5V	4050BD_10V	4066BT_10V
4041BD_15V	4043BP_5V	4050BD_15V	4066BT_15V
4041BD_5V	4043BT_10V	4050BD_5V	4066BT_5V
4041BP_10V	4043BT_15V	4050BP_10V	4068BD_10V
4041BP_15V	4043BT_5V	4050BP_15V	4068BD_15V
4041BP_5V	4044BD_10V	4050BP_5V	4068BD_5V
4041BP_5V	4044BD_15V	4050BP_5V	4068BP_10V
4041BT_10V	4044BD_5V	4050BT_10V	4068BP_15V
4041BT_15V	4044BP_10V	4050BT_15V	4068BP_5V
4041BT_5V	4044BP_15V	4050BT_5V	4068BP_5V
4042BD_10V	4044BP_5V	4060BD_10V	4068BT_10V
4042BD_15V	4044BP_5V	4060BD_15V	4068BT_15V
4042BD_5V	4044BT_10V	4060BD_5V	4068BT_5V
4042BP_10V	4044BT_15V	4060BP_10V	4069BCL_10V
4042BP_15V	4044BT_5V	4060BP_15V	4069BCL_15V
4042BP_5V	4049BD_10V	4060BP_5V	4069BCL_5V
4042BP_5V	4049BD_15V	4060BT_10V	4069BCP_10V
4042BT_10V	4049BD_5V	4060BT_15V	4069BCP_15V
4042BT_15V	4049BP_10V	4060BT_5V	4069BCP_5V
4042BT_5V	4049BP_15V	4066BD_10V	4069BCP_5V

Multisim 14.0 Power Pro Components

4069BD_10V	4072BD_5V	4075BT_10V	4078BD_5V
4069BD_15V	4072BP_10V	4075BT_15V	4078BP_10V
4069BD_5V	4072BP_15V	4075BT_5V	4078BP_15V
4070BD_10V	4072BP_5V	4076BD_10V	4078BP_5V
4070BD_15V	4072BP_5V	4076BD_15V	4078BP_5V
4070BD_5V	4072BT_10V	4076BD_5V	4078BT_10V
4070BP_10V	4072BT_15V	4076BD_5V	4078BT_15V
4070BP_15V	4072BT_5V	4076BP_10V	4078BT_5V
4070BP_5V	4073BD_10V	4076BP_15V	4081BD_10V
4070BP_5V	4073BD_15V	4076BP_5V	4081BD_15V
4070BT_10V	4073BD_5V	4076BT_10V	4081BD_5V
4070BT_15V	4073BP_10V	4076BT_15V	4081BP_10V
4070BT_5V	4073BP_15V	4076BT_5V	4081BP_15V
4071BD_10V	4073BP_5V	4077BD_10V	4081BP_5V
4071BD_15V	4073BP_5V	4077BD_15V	4081BP_5V
4071BD_5V	4073BT_10V	4077BD_5V	4081BT_10V
4071BP_10V	4073BT_15V	4077BP_10V	4081BT_15V
4071BP_15V	4073BT_5V	4077BP_15V	4081BT_5V
4071BP_5V	4075BD_10V	4077BP_5V	4082BD_10V
4071BP_5V	4075BD_15V	4077BP_5V	4082BD_15V
4071BT_10V	4075BD_5V	4077BT_10V	4082BD_5V
4071BT_15V	4075BP_10V	4077BT_15V	4082BP_10V
4071BT_5V	4075BP_15V	4077BT_5V	4082BP_15V
4072BD_10V	4075BP_5V	4078BD_10V	4082BP_5V
4072BD_15V	4075BP_5V	4078BD_15V	4082BP_5V

Multisim 14.0 Power Pro Components

4082BT_10V	4093BD_5V	4099BDW_5V	430 pF [C0402C431K3HACT U]
4082BT_15V	4093BP_10V	40EPS08	
4082BT_5V	4093BP_15V	40EPS12	430 pF [C0402C431K5HACT U]
4085BD_10V	4093BP_5V	40EPS16	
4085BD_15V	4093BP_5V	413990-1	430 pF [C0603C431K1HACT U]
4085BD_5V	4093BT_10V	43 mF [C0805C439KBGAC TU]	
4085BP_10V	4093BT_15V		430 pF [C0603C431K3HACT U]
4085BP_15V	4093BT_5V	43 pF [C0805C430KBGAC TU]	
4085BP_5V	4094BD_10V		430 pF [C0603C431K5HACT U]
4085BP_5V	4094BD_15V	43 pF [C1206C430KBGAC TU]	
4085BT_10V	4094BD_5V		430 pF [C1206C431KBGAC TU]
4085BT_15V	4094BP_10V	43 pF [C1210C430KBGAC TU]	
4085BT_5V	4094BP_15V		430 pF [C1210C431KBGAC TU]
4086BD_10V	4094BP_5V	43 pF [C1812C430KBGAC TU]	
4086BD_15V	4094BT_10V		430 pF [C1812C431KBGAC TU]
4086BD_5V	4094BT_15V	43 pF [C1825C430KBGAC TU]	
4086BD_5V	4094BT_5V		430 pF [C1825C431KBGAC TU]
4086BP_10V	4099BCL_10V	43 pF [C2220C430KBGAC TU]	
4086BP_15V	4099BCL_15V		430 pF [C2220C431KBGAC TU]
4086BP_5V	4099BCL_5V	43 pF [C2225C430KBGAC TU]	
4086BT_10V	4099BCP_10V		430 pF [C2225C431KBGAC TU]
4086BT_15V	4099BCP_15V	430 pF [C0402C431K1HACT U]	
4086BT_5V	4099BCP_5V		4502BD_10V
4093BD_10V	4099BDW_10V		
4093BD_15V	4099BDW_15V		

Multisim 14.0 Power Pro Components

4502BD_15V	4508BP_5V	4512BD_15V	4515BP_5V
4502BD_5V	4508BT_10V	4512BD_5V	4515BT_10V
4502BP_10V	4508BT_15V	4512BP_10V	4515BT_15V
4502BP_15V	4508BT_5V	4512BP_15V	4515BT_5V
4502BP_5V	4510BD_10V	4512BP_5V	4516BD_10V
4502BP_5V	4510BD_15V	4512BP_5V	4516BD_15V
4502BT_10V	4510BD_5V	4512BT_10V	4516BD_5V
4502BT_15V	4510BP_10V	4512BT_15V	4516BP_10V
4502BT_5V	4510BP_15V	4512BT_5V	4516BP_15V
4503BCL_10V	4510BP_5V	4514BD_10V	4516BP_5V
4503BCL_15V	4510BP_5V	4514BD_15V	4516BP_5V
4503BCL_5V	4510BT_10V	4514BD_5V	4516BT_10V
4503BCP_10V	4510BT_15V	4514BP_10V	4516BT_15V
4503BCP_15V	4510BT_5V	4514BP_15V	4516BT_5V
4503BCP_5V	4511BD_10V	4514BP_5V	4518BD_10V
4503BCP_5V	4511BD_15V	4514BP_5V	4518BD_15V
4503BD_10V	4511BD_5V	4514BT_10V	4518BD_5V
4503BD_15V	4511BP_10V	4514BT_15V	4518BP_10V
4503BD_5V	4511BP_15V	4514BT_5V	4518BP_15V
4508BD_10V	4511BP_5V	4515BD_10V	4518BP_5V
4508BD_15V	4511BP_5V	4515BD_15V	4518BP_5V
4508BD_5V	4511BT_10V	4515BD_5V	4518BT_10V
4508BP_10V	4511BT_15V	4515BP_10V	4518BT_15V
4508BP_15V	4511BT_5V	4515BP_15V	4518BT_5V
4508BP_5V	4512BD_10V	4515BP_5V	4519BD_10V

Multisim 14.0 Power Pro Components

4519BD_15V	4522BT_15V	4532BP_5V	4544BCL_5V
4519BD_5V	4522BT_5V	4532BP_5V	4544BCP_10V
4519BP_10V	4526BD_10V	4532BT_10V	4544BCP_15V
4519BP_15V	4526BD_15V	4532BT_15V	4544BCP_5V
4519BP_5V	4526BD_5V	4532BT_5V	4555BD_10V
4519BT_10V	4526BP_10V	4539BD_10V	4555BD_15V
4519BT_15V	4526BP_15V	4539BD_15V	4555BD_5V
4519BT_5V	4526BP_5V	4539BD_5V	4555BP_10V
4520BD_10V	4526BT_10V	4539BP_10V	4555BP_15V
4520BD_15V	4526BT_15V	4539BP_15V	4555BP_5V
4520BD_5V	4526BT_5V	4539BP_5V	4555BT_10V
4520BP_10V	4531BD_10V	4539BT_10V	4555BT_15V
4520BP_15V	4531BD_15V	4539BT_15V	4555BT_5V
4520BP_5V	4531BD_5V	4539BT_5V	4556BD_10V
4520BP_5V	4531BP_10V	4543BD_10V	4556BD_15V
4520BT_10V	4531BP_15V	4543BD_15V	4556BD_5V
4520BT_15V	4531BP_5V	4543BD_5V	4556BP_10V
4520BT_5V	4531BT_10V	4543BP_10V	4556BP_15V
4522BD_10V	4531BT_15V	4543BP_15V	4556BP_5V
4522BD_15V	4531BT_5V	4543BP_5V	4556BP_5V
4522BD_5V	4532BD_10V	4543BT_10V	4556BT_10V
4522BP_10V	4532BD_15V	4543BT_15V	4556BT_15V
4522BP_15V	4532BD_5V	4543BT_5V	4556BT_5V
4522BP_5V	4532BP_10V	4544BCL_10V	4585BD_10V
4522BT_10V	4532BP_15V	4544BCL_15V	4585BD_15V

Multisim 14.0 Power Pro Components

4585BD_5V	47 nF [C0402C473K8RACT U]	47 nF [C0805C473K1RACT U]	47 nF [C1206C473K1RACT U]
4585BP_10V			
4585BP_15V	47 nF [C0402C473K9PACT U]	47 nF [C0805C473K3RACT U]	47 nF [C1206C473K3GACT U]
4585BP_5V			
4585BT_10V	47 nF [C0402C473K9RACT U]	47 nF [C0805C473K4RACT U]	47 nF [C1206C473K3HACT U]
4585BT_15V			
4585BT_5V			
45970-4185	47 nF [C0603C473K1RACT U]	47 nF [C0805C473K5RACT U]	47 nF [C1206C473K3RACT U]
4-644456-0			
46765-1001	47 nF [C0603C473K3NAC TU]	47 nF [C0805C473K8RACT U]	47 nF [C1206C473K4RACT U]
46765-2001			
47 mF [C0805C479KBGAC TU]	47 nF [C0603C473K3RACT U]	47 nF [C0805C473M5UAC TU]	47 nF [C1206C473K5HACT U]
47 mF [C1206C479K1GACT U]	47 nF [C0603C473K4RACT U]	47 nF [C0805C473M5VAC TU]	47 nF [C1206C473K5RACT U]
47 nF [C0402C473K3RACT U]	47 nF [C0603C473K5NAC TU]	47 nF [C0805F473K3RACT U]	47 nF [C1206C473KARACT U]
47 nF [C0402C473K4PACT U]	47 nF [C0603C473K5RACT U]	47 nF [C0805F473K4RACT U]	47 nF [C1206C473M5UAC TU]
47 nF [C0402C473K4RACT U]	47 nF [C0603C473K8RACT U]	47 nF [C0805F473K5RACT U]	47 nF [C1206F473K1RACT U]
47 nF [C0402C473K8PACT U]	47 nF [C0603C473M3VAC TU]	47 nF [C1206C473K1HACT U]	47 nF [C1206F473K3RACT U]

Multisim 14.0 Power Pro Components

47 nF [C1206F473K4RACT U]	47 nF [C1210C473KARACT U]	47 nF [C2220C473K5GACT U]	47 pF [C0805C470K1GACT U]
47 nF [C1206F473K5RACT U]	47 nF [C1812C473K1GACT U]	47 nF [CA064C473K4RACT U]	47 pF [C0805C470K2GACT U]
47 nF [C1210C473K1GACT U]	47 nF [C1812C473K1HACT U]	47 nF [CA064C473K8RACT U]	47 pF [C0805C470K3GACT U]
47 nF [C1210C473K1HACT U]	47 nF [C1812C473K1RACT U]	47 pF [C0201C470K3GACT U]	47 pF [C0805C470K5GACT U]
47 nF [C1210C473K1RACT U]	47 nF [C1812C473K2RACT U]	47 pF [C0402C470K3GACT U]	47 pF [C0805C470KBGAC TU]
47 nF [C1210C473K2RACT U]	47 nF [C1812C473K5GACT U]	47 pF [C0402C470K4GACT U]	47 pF [C0805C470KCGAC TU]
47 nF [C1210C473K3GACT U]	47 nF [C1812C473K5HACT U]	47 pF [C0402C470K5GACT U]	47 pF [C1206C470K1GACT U]
47 nF [C1210C473K3HACT U]	47 nF [C1812C473K5RACT U]	47 pF [C0402C470K8GACT U]	47 pF [C1206C470K2GACT U]
47 nF [C1210C473K5GACT U]	47 nF [C1825C473K5RACT U]	47 pF [C0603C470K1GACT U]	47 pF [C1206C470K3GACT U]
47 nF [C1210C473K5HACT U]	47 nF [C2220C473K1GACT U]	47 pF [C0603C470K5GACT U]	47 pF [C1206C470K5GACT U]
47 nF [C1210C473K5RACT U]	47 nF [C2220C473K2GACT U]	47 pF [C0603C470K8GACT U]	47 pF [C1206C470KBGAC TU]

Multisim 14.0 Power Pro Components

47 pF [C1206C470KDGAC TU]	47 pF [CA064C470K5GAC TU]	47 uF [T491C476M006AT]	47 uF [T491U476M006AT]
47 pF [C1206C470KFGACT U]	47 pF [CA064C470K8GAC TU]	47 uF [T491C476M010AT]	47 uF [T491U476M010AT]
47 pF [C1206C470KGGAC TU]	47 uF [A700V476M006AT E018]	47 uF [T491C476M020AT]	47 uF [T491V476M010AT]
47 pF [C1210C470K5GACT U]	47 uF [A700V476M006AT E025]	47 uF [T491D476M006AT]	47 uF [T491V476M016AT]
47 pF [C1210C470KBGAC TU]	47 uF [A700V476M006AT E028]	47 uF [T491D476M010AT]	47 uF [T491X476M025AT]
47 pF [C1812C470KBGAC TU]	47 uF [T409H476M010AH 4250]	47 uF [T491D476M016AT]	47 uF [T494A476M004AT]
47 pF [C1812C470KDGAC TU]	47 uF [T419F476M010AH 4250]	47 uF [T491D476M020AT]	47 uF [T494A476M006AT]
47 pF [C1825C470KBGAC TU]	47 uF [T491A476M004AT]	47 uF [T491D476M025AT]	47 uF [T494B476M004AT]
47 pF [C2220C470KBGAC TU]	47 uF [T491A476M006AT]	47 uF [T491E476M035AT]	47 uF [T494B476M010AT]
47 pF [C2225C470KBGAC TU]	47 uF [T491B476M004AT]	47 uF [T491T476M004AT]	47 uF [T494C476M004AT]
47 pF [CA064C470K3GAC TU]	47 uF [T491B476M006AT]	47 uF [T491T476M006AT]	47 uF [T494C476M006AT]
	47 uF [T491B476M010AT]	47 uF [T491U476M004AT]	47 uF [T494C476M010AT]
	47 uF [T491C476M004AT]		47 uF [T494C476M016AT]

Multisim 14.0 Power Pro Components

47 uF [T494C476M020AT]	47 uF [T494V476M010AT]	47 uF [T495D476M016AT E150]	47 uF [T495X476M025AT E185]
47 uF [T494D476M006AT]	47 uF [T494V476M016AT]	47 uF [T495D476M020AT E100]	47 uF [T495X476M025AT E200]
47 uF [T494D476M010AT]	47 uF [T494X476M025AT]	47 uF [T495D476M020AT E175]	47 uF [T495X476M035AT E185]
47 uF [T494D476M016AT]	47 uF [T495B476M006AT E450]	47 uF [T495D476M025AT E120]	47 uF [T495X476M035AT E200]
47 uF [T494D476M020AT]	47 uF [T495B476M010AT E500]	47 uF [T495D476M025AT E250]	47 uF [T495X476M035AT E300]
47 uF [T494D476M025AT]	47 uF [T495C476M016AT E350]	47 uF [T495V476M006AT E150]	47 uF [T497G476M006AT 6110]
47 uF [T494E476M035AT]	47 uF [T495D476M010AT E080]	47 uF [T495X476M020AT E065]	47 uF [T498C476M006AT E800]
47 uF [T494T476M004AT]	47 uF [T495D476M010AT E090]	47 uF [T495X476M020AT E100]	47 uF [T498D476M010AT E600]
47 uF [T494U476M004AT]	47 uF [T495D476M010AT E200]	47 uF [T495X476M020AT E150]	47 uF [T498D476M016AT E600]
47 uF [T494U476M006AT]	47 uF [T495D476M016AT E080]	47 uF [T495X476M025AT E080]	47 uF [T510E476M035AT E050]
47 uF [T494U476M010AT]	47 uF [T495D476M016AT E100]	47 uF [T495X476M025AT E150]	47 uF [T510X476M035AT E055]

Multisim 14.0 Power Pro Components

47 uF [T510X476M035AT E065]	47 uF [T520B476M010AT E035]	47 uF [T520W476M016AT E045]	47 uF [T543W476M016AT E045]
47 uF [T520A476M004AT E070]	47 uF [T520B476M010AT E070]	47 uF [T521D476M020AT E055]	470 nF [C0402C474K9PACT U]
47 uF [T520A476M004AT E080]	47 uF [T520C476M010AT E100]	47 uF [T521V476M020AT E090]	470 nF [C0603C474K4PACT U]
47 uF [T520A476M006AT E150]	47 uF [T520D476M016AT E035]	47 uF [T521W476M020AT E045]	470 nF [C0603C474K4RACT U]
47 uF [T520A476M2R5AT E090]	47 uF [T520D476M016AT E070]	47 uF [T521X476M035AT E030]	470 nF [C0603C474K8PACT U]
47 uF [T520B476M006AT E025]	47 uF [T520Q476M011AT E040]	47 uF [T521X476M035AT E070]	470 nF [C0603C474K8RACT U]
47 uF [T520B476M006AT E035]	47 uF [T520T476M004AT E070]	47 uF [T525B476M006AT E080]	470 nF [C0603C474K9PACT U]
47 uF [T520B476M006AT E040]	47 uF [T520T476M006AT E040]	47 uF [T525D476M016AT E035]	470 nF [C0603C474K9RACT U]
47 uF [T520B476M006AT E070]	47 uF [T520T476M006AT E070]	47 uF [T525D476M016AT E065]	470 nF [C0805C474K3NAC TU]
47 uF [T520B476M008AT E035]	47 uF [T520V476M016AT E045]	47 uF [T525T476M006AT E080]	470 nF [C0805C474K3PACT U]
47 uF [T520B476M008AT E070]	47 uF [T520V476M016AT E070]	47 uF [T543A476M004AT E080]	470 nF [C0805C474K3RACT U]

Multisim 14.0 Power Pro Components

470 nF [C0805C474K4RACT U]	470 nF [C1206C474M4VAC TU]	470 nF [C1812C474K5RACT U]	470 nF [C2220C474KARACT U]
470 nF [C0805C474K8RACT U]	470 nF [C1206F474K3RACT U]	470 nF [C1812C474KARACT U]	470 nF [C2225C474K1RACT U]
470 nF [C0805C474M3VAC TU]	470 nF [C1206F474K4RACT U]	470 nF [C1812C474M5UAC TU]	470 nF [C2225C474K2RACT U]
470 nF [C0805C474M4VAC TU]	470 nF [C1210C474K3RACT U]	470 nF [C1812F474K1RACT U]	470 nF [C2225C474K5RACT U]
470 nF [C1206C474K3NAC TU]	470 nF [C1210C474K4RACT U]	470 nF [C1812F474K3RACT U]	470 nF [C2225C474KARACT U]
470 nF [C1206C474K3RACT U]	470 nF [C1210C474K5RACT U]	470 nF [C1812F474K5RACT U]	470 nF [C2225C474M1UAC TU]
470 nF [C1206C474K4RACT U]	470 nF [C1210C474M5UAC TU]	470 nF [C1825C474K1RACT U]	470 nF [CDR06BX474AKSM]
470 nF [C1206C474K5NAC TU]	470 nF [C1210F474K1RACT U]	470 nF [C1825C474K5RACT U]	470 nF [T491A474M025AT]
470 nF [C1206C474K5RACT U]	470 nF [C1210F474K3RACT U]	470 nF [C1825C474KARACT U]	470 nF [T491A474M035AT]
470 nF [C1206C474K8RACT U]	470 nF [C1210F474K4RACT U]	470 nF [C2220C474K1RACT U]	470 nF [T491B474M035AT]
470 nF [C1206C474M3VAC TU]	470 nF [C1210F474K5RACT U]	470 nF [C2220C474K5RACT U]	470 nF [T491B474M050AT]
			470 nF [T491C474M050AT]
			470 nF [T494A474M025AT]

Multisim 14.0 Power Pro Components

470 nF [T494A474M035AT]	470 pF [C0402C471K8RACT U]	470 pF [C0603C471K5RACT U]	470 pF [C1206C471K1GACT U]
470 nF [T494B474M035AT]	470 pF [C0402C471K9RACT U]	470 pF [C0603C471K8RACT U]	470 pF [C1206C471K2GACT U]
470 nF [T494B474M050AT]	470 pF [C0603C471K1HACT U]	470 pF [C0805C471K1GACT U]	470 pF [C1206C471K5GACT U]
470 nF [T498A474M025AT E8K5]	470 pF [C0603C471K1RACT U]	470 pF [C0805C471K1RACT U]	470 pF [C1206C471KBGAC TU]
470 pF [C0402C471K1HACT U]	470 pF [C0603C471K2RACT U]	470 pF [C0805C471K2GACT U]	470 pF [C1206C471KCGAC TU]
470 pF [C0402C471K3GACT U]	470 pF [C0603C471K3GACT U]	470 pF [C0805C471K2RACT U]	470 pF [C1210C471K5GACT U]
470 pF [C0402C471K3HACT U]	470 pF [C0603C471K3HACT U]	470 pF [C0805C471K3RACT U]	470 pF [C1210C471KBGAC TU]
470 pF [C0402C471K3RACT U]	470 pF [C0603C471K3RACT U]	470 pF [C0805C471K4RACT U]	470 pF [C1210C471KCGAC TU]
470 pF [C0402C471K4RACT U]	470 pF [C0603C471K4RACT U]	470 pF [C0805C471K5GACT U]	470 pF [C1812C471K5GACT U]
470 pF [C0402C471K5HACT U]	470 pF [C0603C471K5GACT U]	470 pF [C0805C471K5RACT U]	470 pF [C1812C471KBGAC TU]
470 pF [C0402C471K5RACT U]	470 pF [C0603C471K5HACT U]	470 pF [C0805C471KARACT U]	470 pF [C1825C471KBGAC TU]

Multisim 14.0 Power Pro Components

470 pF [C2220C471KBGAC TU]	470 uF [T491D477M006AT]	470 uF [T495D477M006AT E100]	470 uF [T495X477M010AT E050]
470 pF [C2225C471KBGAC TU]	470 uF [T491E477M006AT]	470 uF [T495D477M006AT E125]	470 uF [T495X477M010AT E060]
470 pF [CA064C471K4RACT U]	470 uF [T491E477M010AT] 470 uF [T491X477M004AT]	470 uF [T495E477M006AT E040]	470 uF [T495X477M010AT E100]
470 pF [CA064C471K5GAC TU]	470 uF [T491X477M006AT]	470 uF [T495X477M004AT E030]	470 uF [T495X477M010AT E200]
470 pF [CA064C471K5RACT U]	470 uF [T491X477M010AT] 470 uF [T494D477M004AT]	470 uF [T495X477M004AT E045]	470 uF [T510X477M006AT E030]
470 pF [CA064C471K8RAC]	470 uF [T494D477M006AT]	470 uF [T495X477M004AT E100]	470 uF [T513X477M006AH 6110]
470 uF [A700X477M002AT E007]	470 uF [T494D477M006AT]	470 uF [T495X477M006AT E030]	470 uF [T520C477M2R5AT E025]
470 uF [A700X477M002AT E010]	470 uF [T494E477M006AT] 470 uF [T494E477M010AT]	470 uF [T495X477M006AT E045]	470 uF [T520C477M2R5AT E045]
470 uF [A700X477M002AT E015]	470 uF [T494X477M004AT]	470 uF [T495X477M006AT E050]	470 uF [T520D477M004AT E010]
470 uF [T489X477M006AT E200]	470 uF [T494X477M006AT]	470 uF [T495X477M006AT E065]	470 uF [T520D477M004AT E012]
470 uF [T491D477M004AT]	470 uF [T494X477M010AT] 470 uF [T495D477M006AT E045]	470 uF [T495X477M010AT E045]	470 uF [T520D477M004AT E015]

Multisim 14.0 Power Pro Components

470 uF [T520D477M004AT E018]	470 uF [T520V477M2R5AT E012]	470 uF [T520Y477M006AT E025]	470 uF [T530D477M2R5AT E006]
470 uF [T520D477M004AT E025]	470 uF [T520V477M2R5AT E015]	470 uF [T522Y477M006AT E040]	470 uF [T530X477M006AT E004]
470 uF [T520D477M004AT E040]	470 uF [T520V477M2R5AT E018]	470 uF [T525D477M003AT E025]	470 uF [T530X477M006AT E005]
470 uF [T520D477M006AT E025]	470 uF [T520W477M006AT E055]	470 uF [T525D477M004AT E025]	470 uF [T530X477M006AT E006]
470 uF [T520D477M006AT E030]	470 uF [T520X477M006AT E010]	470 uF [T525D477M004AT E040]	470 uF [T530X477M006AT E010]
470 uF [T520D477M2R5AT E006]	470 uF [T520X477M006AT E018]	470 uF [T525D477M2R5AT E025]	470 uF [T530Y477M004AT E005]
470 uF [T520D477M2R5AT E007]	470 uF [T520X477M006AT E035]	470 uF [T528Z477M2R5AT E005]	470 uF [T530Y477M006AT E005]
470 uF [T520D477M2R5AT E009]	470 uF [T520X477M006AT E040]	470 uF [T528Z477M2R5AT E009]	470 uF [T543D477M2R5AT E007]
470 uF [T520V477M002AT E040]	470 uF [T520Y477M006AT E010]	470 uF [T528Z477M2R5AT E012]	47151-0001
470 uF [T520V477M2R5AT E007]	470 uF [T520Y477M006AT E015]	470 uF [T530D477M004AT E006]	47272-0001
470 uF [T520V477M2R5AT E009]	470 uF [T520Y477M006AT E018]	470 uF [T530D477M004AT E010]	4Line_Bussed
			4Line_Isolated
			4Line_Terminator
			4N25
			4N25A

Multisim 14.0 Power Pro Components

4N26	5.1 nF [C0805C512K1HACT U]	5.6 nF [C0603C562K3HACT U]	5.6 nF [C0805C562K3HACT U]
4N27			
4N28	5.1 nF [C0805C512K3HACT U]	5.6 nF [C0603C562K3RACT U]	5.6 nF [C0805C562K3RACT U]
4N33			
4N35	5.1 nF [C0805C512K5HACT U]	5.6 nF [C0603C562K4RACT U]	5.6 nF [C0805C562K4RACT U]
4N36			
4N37	5.1 nF [C1206C512K5GACT U]	5.6 nF [C0603C562K5HACT U]	5.6 nF [C0805C562K5HACT U]
4N38			
4N38A	5.1 nF [C2220C512KBGAC TU]	5.6 nF [C0603C562K5RACT U]	5.6 nF [C0805C562K5RACT U]
4N48			
4N49	5.1 nF [C2225C512KBGAC TU]	5.6 nF [C0603C562K8RACT U]	5.6 nF [C0805C562K8RACT U]
4P1S			
4P2S	5.6 nF [C0402C562K3RACT U]	5.6 nF [C0805C562K1GACT U]	5.6 nF [C1206C562K1RACT U]
4P3S			
4P4S	5.6 nF [C0402C562K4RACT U]	5.6 nF [C0805C562K1HACT U]	5.6 nF [C1206C562K2RACT U]
4P5S			
4POS_ROTARY	5.6 nF [C0402C562K5RACT U]	5.6 nF [C0805C562K1RACT U]	5.6 nF [C1206C562K5GACT U]
4V_0.5W			
5.1 nF [C0603C512K3HACT U]	5.6 nF [C0402C562K5RACT U]	5.6 nF [C0805C562K1RACT U]	5.6 nF [C1206C562K5GACT U]
5.1 nF [C0603C512K5HACT U]	5.6 nF [C0603C562K1RACT U]	5.6 nF [C0805C562K2RACT U]	5.6 nF [C1206C562K5RACT U]
5.1 nF [C0805C512K1GACT U]	5.6 nF [C0603C562K3GACT U]	5.6 nF [C0805C562K3GACT U]	5.6 nF [C1206C562KARACT U]

Multisim 14.0 Power Pro Components

5.6 nF [C1210C562K5GACT U]	50_AMP 5082_3001	51 pF [C0805C510K1GACT U]	51 pF [C2225C510KBGAC TU]
5.6 nF [C1210C562K5RACT U]	5082_3039 5082_3042	51 pF [C0805C510K2GACT U]	510 pF [C0402C511K1HACT U]
5.6 nF [C1210C562KARACT U]	5082_3077 5082_3080	51 pF [C0805C510K5GACT U]	510 pF [C0402C511K3HACT U]
5.6 nF [C1812C562K2GACT U]	5082_3101 5082_3201	51 pF [C0805C510KBGAC TU]	510 pF [C0402C511K5HACT U]
5.6 nF [C2220C562KBGAC TU]	5082_3303 5082_3900	51 pF [C0805C510KCGAC TU]	510 pF [C0603C511K1HACT U]
5.6 nF [C2225C562KBGAC TU]	50A02CH-TL-E 50C02CH-TL-E	51 pF [C1206C510K5GACT U]	510 pF [C0603C511K3HACT U]
5.6 uF [C0805C565K9PACT U]	51 mF [C0805C519K3GACT U]	51 pF [C1206C510KBGAC TU]	510 pF [C0603C511K5GACT U]
5.6 uF [C1206C565K4RACT U]	51 mF [C0805C519KBGAC TU]	51 pF [C1210C510KBGAC TU]	510 pF [C0603C511K5HACT U]
5.6 uF [C1206C565K8RACT U]	51 pF [C0402C510K5GACT U]	51 pF [C1812C510KBGAC TU]	510 pF [C0603C511K8GACT U]
5.6 uF [C1206C565K9RACT U]	51 pF [C0603C510K2GACT U]	51 pF [C1825C510KBGAC TU]	510 pF [C0805C511K5GACT U]
5.6 uF [C1210C565K4PACT U]	51 pF [C0603C510K5GACT U]	51 pF [C2220C510KBGAC TU]	510 pF [C1206C511K1GACT U]

5_AMP

Multisim 14.0 Power Pro Components

510 pF [C1206C511KBGAC TU]	5227677-1 532903-2	56 nF [C0603C563K4RACT U]	56 nF [C1206C563K1RACT U]
510 pF [C1210C511KBGAC TU]	532903-6 534206-5	56 nF [C0603C563K5RACT U]	56 nF [C1206C563K3HACT U]
510 pF [C1812C511KBGAC TU]	534237-3 534237-6	56 nF [C0805C563K1RACT U]	56 nF [C1206C563K3RACT U]
510 pF [C1825C511KBGAC TU]	534237-8 5414337-1	56 nF [C0805C563K2RACT U]	56 nF [C1206C563K5HACT U]
510 pF [C2220C511KBGAC TU]	54ACT16245WD 54F545DM	56 nF [C0805C563K3RACT U]	56 nF [C1206C563K5RACT U]
510 pF [C2225C511KBGAC TU]	54F545LM 555_TIMER_RATED	56 nF [C0805C563K4RACT U]	56 nF [C1206C563KARACT U]
5103309-1	555_VIRTUAL 5558067-1	56 nF [C0805C563K5RACT U]	56 nF [C1206C563M5UAC TU]
5103309-5	56 mF [C0805C569KBGAC TU]	56 nF [C0805C563K8RACT U]	56 nF [C1206F563K1RACT U]
5103309-6	56 nF [C0402C563K4RACT U]	56 nF [C0805F563K3RACT U]	56 nF [C1206F563K3RACT U]
5103309-7	56 nF [C0402C563K8RACT U]	56 nF [C0805F563K4RACT U]	56 nF [C1206F563K4RACT U]
5103309-8	56 nF [C0402C563K9RACT U]	56 nF [C0805F563K5RACT U]	56 nF [C1206F563K5RACT U]
5103310-1	56 nF [C0402C563K8RACT U]		
5103310-5	56 nF [C0402C563K9RACT U]		
5103310-6	56 nF [C0402C563K9RACT U]		
5103310-7	56 nF [C0603C563K3RACT U]		
5103310-8			
5-1814400-1			
5227222-3			

Multisim 14.0 Power Pro Components

56 nF [C1210C563K1GACT U]	56 nF [C1812C563K1RACT U]	56 pF [C0603C560K1GACT U]	56 pF [C1206C560K5GACT U]
56 nF [C1210C563K1HACT U]	56 nF [C1812C563K5GACT U]	56 pF [C0603C560K2GACT U]	56 pF [C1206C560KBGAC TU]
56 nF [C1210C563K1RACT U]	56 nF [C1812C563K5HACT U]	56 pF [C0603C560K3GACT U]	56 pF [C1206C560KDGAC TU]
56 nF [C1210C563K2RACT U]	56 nF [C2220C563K1GACT U]	56 pF [C0603C560K5GACT U]	56 pF [C1210C560KBGAC TU]
56 nF [C1210C563K3HACT U]	56 nF [C2220C563K2GACT U]	56 pF [C0805C560K1GACT U]	56 pF [C1812C560KBGAC TU]
56 nF [C1210C563K5GACT U]	56 nF [C2220C563K5GACT U]	56 pF [C0805C560K2GACT U]	56 pF [C1812C560KHGAC TU]
56 nF [C1210C563K5HACT U]	56 pF [C0201C560K3GACT U]	56 pF [C0805C560K5GACT U]	56 pF [C1825C560KBGAC TU]
56 nF [C1210C563K5RACT U]	56 pF [C0201C560K8GACT U]	56 pF [C0805C560KBGAC TU]	56 pF [C2220C560KBGAC TU]
56 nF [C1210C563KARACT U]	56 pF [C0402C560K3GACT U]	56 pF [C0805C560KDGAC TU]	56 pF [C2225C560KBGAC TU]
56 nF [C1812C563K1GACT U]	56 pF [C0402C560K5GACT U]	56 pF [C1206C560K1GACT U]	56 pF [CA064C560K5GAC TU]
56 nF [C1812C563K1HACT U]	56 pF [C0402C560K8GACT U]	56 pF [C1206C560K2GACT U]	56 uF [A700D566M008AT E015]

Multisim 14.0 Power Pro Components

56 uF [A700D566M008AT E018]	560 nF [C0805C564K8RACT U]	560 nF [C1812F564K3RACT U]	560 pF [C0402C561K3HACT U]
56 uF [A700D566M010AT E015]	560 nF [C1206C564K3RACT U]	560 nF [C1812F564K5RACT U]	560 pF [C0402C561K3RACT U]
56 uF [A700D566M010AT E018]	560 nF [C1206C564K4RACT U]	560 nF [C1825C564K5RACT U]	560 pF [C0402C561K4RACT U]
56 uF [A700V566M006AT E018]	560 nF [C1206C564K5RACT U]	560 nF [C1825C564KARACT U]	560 pF [C0402C561K5HACT U]
56 uF [A700V566M006AT E025]	560 nF [C1206F564K4RACT U]	560 nF [C2220C564K1RACT U]	560 pF [C0402C561K5RACT U]
56 uF [A700V566M006AT E028]	560 nF [C1210C564K5RACT U]	560 nF [C2220C564K5RACT U]	560 pF [C0402C561K8RACT U]
56 uF [T520T566M2R5AT E040]	560 nF [C1210F564K3RACT U]	560 nF [C2220C564KARACT U]	560 pF [C0603C561K1HACT U]
56 uF [T520T566M2R5AT E070]	560 nF [C1210F564K4RACT U]	560 nF [C2225C564K5RACT U]	560 pF [C0603C561K1RACT U]
560 nF [C0603C564K8PACT U]	560 nF [C1210F564K5RACT U]	560 nF [C2225C564KARACT U]	560 pF [C0603C561K2RACT U]
560 nF [C0805C564K3RACT U]	560 nF [C1812C564K5RACT U]	560 pF [C0402C561K1HACT U]	560 pF [C0603C561K3HACT U]
560 nF [C0805C564K4RACT U]	560 nF [C1812F564K1RACT U]	560 pF [C0402C561K3GACT U]	560 pF [C0603C561K3RACT U]

Multisim 14.0 Power Pro Components

560 pF [C0603C561K4RACT U]	560 pF [C0805C561K8RACT U]	560 uF [T530D567M2R5AT E005]	5Line_Bussed 5Line_Isolated 5LN01C-TB-E 5LN01C-TB-H 5LN01M-TL-E 5LN01M-TL-H 5LN01SP-AC 5LN01SS-TL-E 5LN01SS-TL-H 5LN01S-TL-E 5P1S 5P2S 5P3S 5P4S 5P5S 5POS_ROTARY 5U4GB 5V_1W 5V3A 5V4GA 5Y3GT 6.2 nF [C0603C622K3HACT U]
560 pF [C0603C561K5GACT U]	560 pF [C1206C561K1GACT U]	5687169-9 571-0100 571-0200 571-0300 571-0400 571-0500 571-0600 571-0700 5AR4 5EQ100 5KP10A-E3/54 5KP16A-E3/54 5KP18A-E3/54 5KP22A-E3/54 5KP24A-E3/54 5KP28A-E3/54 5KP30A-E3/54 5KP33A-E3/54 5KP40A-E3/54 5KP48A-E3/54 5KP58A-E3/54 5KP60A-E3/54 5KP85A-E3/54	
560 pF [C0603C561K5HACT U]	560 pF [C1206C561K2GACT U]		
560 pF [C0603C561K5RACT U]	560 pF [C1206C561K5GACT U]		
560 pF [C0603C561K8RACT U]	560 pF [C1206C561KBGAC TU]		
560 pF [C0805C561K1GACT U]	560 pF [C1210C561KBGAC TU]		
560 pF [C0805C561K1RACT U]	560 pF [C1812C561KBGAC TU]		
560 pF [C0805C561K2RACT U]	560 pF [C1825C561KBGAC TU]		
560 pF [C0805C561K4RACT U]	560 pF [C2220C561KBGAC TU]		
560 pF [C0805C561K5GACT U]	560 pF [C2225C561KBGAC TU]		
560 pF [C0805C561K5RACT U]	560 pF [CA064C561K2RACT U]		

Multisim 14.0 Power Pro Components

6.2 nF [C0603C622K5HACT U]	6.8 nF [C0603C682K2RACT U]	6.8 nF [C0805C682K3GACT U]	6.8 nF [C1206C682K3RACT U]
6.2 nF [C0805C622K1GACT U]	6.8 nF [C0603C682K3GACT U]	6.8 nF [C0805C682K3HACT U]	6.8 nF [C1206C682K5HACT U]
6.2 nF [C0805C622K1HACT U]	6.8 nF [C0603C682K3HACT U]	6.8 nF [C0805C682K3RACT U]	6.8 nF [C1206C682K5RACT U]
6.2 nF [C0805C622K3HACT U]	6.8 nF [C0603C682K3RACT U]	6.8 nF [C0805C682K4RACT U]	6.8 nF [C1210C682K1GACT U]
6.2 nF [C0805C622K5HACT U]	6.8 nF [C0603C682K4RACT U]	6.8 nF [C0805C682K5GACT U]	6.8 nF [C1210C682K1RACT U]
6.2 nF [C2225C622KBGAC TU]	6.8 nF [C0603C682K5HACT U]	6.8 nF [C0805C682K5HACT U]	6.8 nF [C1210C682K5GACT U]
6.8 nF [C0402C682K3RACT U]	6.8 nF [C0603C682K5RACT U]	6.8 nF [C0805C682K5RACT U]	6.8 nF [C1210C682K5RACT U]
6.8 nF [C0402C682K4RACT U]	6.8 nF [C0603C682K8RACT U]	6.8 nF [C1206C682K1HACT U]	6.8 nF [C1210C682KARACT U]
6.8 nF [C0402C682K5RACT U]	6.8 nF [C0805C682K1GACT U]	6.8 nF [C1206C682K1RACT U]	6.8 nF [C1812C682K1GACT U]
6.8 nF [C0402C682K8RACT U]	6.8 nF [C0805C682K1HACT U]	6.8 nF [C1206C682K3GACT U]	6.8 nF [C1812C682K1RACT U]
6.8 nF [C0603C682K1RACT U]	6.8 nF [C0805C682K1RACT U]	6.8 nF [C1206C682K3HACT U]	6.8 nF [C1812C682K5GACT U]

Multisim 14.0 Power Pro Components

6.8 nF [C1812C682K5RACT U]	6.8 uF [C1206C685K9RACT U]	6.8 uF [T491A685M016AT]	6.8 uF [T491T685M010AT]
6.8 nF [C2220C682K2GACT U]	6.8 uF [C1210C685K3PACT U]	6.8 uF [T491A685M020AT]	6.8 uF [T491U685M020AT]
6.8 nF [C2225C682KBGAC TU]	6.8 uF [C1210C685K4PACT U]	6.8 uF [T491B685M006AT]	6.8 uF [T491X685M050AT]
6.8 nF [CDR06BP682BKSM]	6.8 uF [C1210C685K8PACT U]	6.8 uF [T491B685M010AT]	6.8 uF [T494A685M004AT]
6.8 uF [A700V685M016AT E070]	6.8 uF [C1210C685M4VAC TU]	6.8 uF [T491B685M016AT]	6.8 uF [T494A685M006AT]
6.8 uF [C0805C685K8PACT U]	6.8 uF [T419B685M006AH 4250]	6.8 uF [T491B685M025AT]	6.8 uF [T494A685M010AT]
6.8 uF [C0805C685K9PACT U]	6.8 uF [T419C685M010AH 4250]	6.8 uF [T491C685M016AT]	6.8 uF [T494A685M016AT]
6.8 uF [C1206C685K4PACT U]	6.8 uF [T419C685M020AT]	6.8 uF [T491C685M025AT]	6.8 uF [T494A685M020AT]
6.8 uF [C0805C685K9PACT U]	6.8 uF [T419C685M035AT]	6.8 uF [T491C685M035AT]	6.8 uF [T494B685M006AT]
6.8 uF [C1206C685K4PACT U]	6.8 uF [T429D685M006AH 4250]	6.8 uF [T491D685M035AT]	6.8 uF [T494B685M010AT]
6.8 uF [C1206C685K4RACT U]	6.8 uF [T489B685M010AT E3K0]	6.8 uF [T491D685M050AT]	6.8 uF [T494B685M016AT]
6.8 uF [C1206C685K8RACT U]	6.8 uF [T491A685M004AT]	6.8 uF [T491D685M050AT]	6.8 uF [T494B685M020AT]
6.8 uF [C1206C685K9PACT U]	6.8 uF [T491A685M006AT]	6.8 uF [T491S685M004AT]	6.8 uF [T494B685M025AT]
	6.8 uF [T491A685M010AT]	6.8 uF [T491S685M006AT]	6.8 uF [T494C685M016AT]
		6.8 uF [T491S685M010AT]	6.8 uF [T494C685M020AT]

Multisim 14.0 Power Pro Components

6.8 uF [T494C685M025AT]	6.8 uF [T495D685M050AT E190]	61729-0010BLF	62 pF [C2225C620KBGAC TU]
6.8 uF [T494C685M035AT]	6.8 uF [T495D685M050AT E200]	62 mF [C0805C629KBGAC TU]	620 pF [C0402C621K1HACT U]
6.8 uF [T494D685M035AT]	6.8 uF [T495D685M050AT E300]	62 pF [C0402C620K3GACT U]	620 pF [C0402C621K3HACT U]
6.8 uF [T494D685M050AT]	6.8 uF [T497B685M010AT 6110]	62 pF [C0603C620K5GACT U]	620 pF [C0402C621K5HACT U]
6.8 uF [T494S685M004AT]	6.8 uF [T498A685M016AT E2K6]	62 pF [C0805C620KBGAC TU]	620 pF [C0603C621K1HACT U]
6.8 uF [T494S685M010AT]	6.8 uF [T498B685M016AT E1K8]	62 pF [C1206C620KBGAC TU]	620 pF [C0603C621K3HACT U]
6.8 uF [T494T685M010AT]	6.8 uF [T498D685M035AT E900]	62 pF [C1206C620KDGAC TU]	620 pF [C0603C621K5GACT U]
6.8 uF [T494U685M020AT]	6.8 uF [T499C685M020AT E1K9]	62 pF [C1210C620KBGAC TU]	620 pF [C0603C621K5HACT U]
6.8 uF [T494X685M050AT]	6.8 uF [T521D685M050AT E090]	62 pF [C1812C620KBGAC TU]	620 pF [C0805C621K5GACT U]
6.8 uF [T495C685M025AT E400]	6.8 uF [T521V685M050AT E090]	62 pF [C1825C620KBGAC TU]	620 pF [C1210C621KBGAC TU]
6.8 uF [T495C685M025AT E500]	608PWM		620 pF [C1812C621KBGAC TU]
6.8 uF [T495D685M035AT E150]	60LQ045	62 pF [C2220C620KBGAC TU]	
	60LQ100		

Multisim 14.0 Power Pro Components

620 pF [C1825C621KBGAC TU]	68 nF [C0402C683K9RACT U]	68 nF [C0805C683K8RACT U]	68 nF [C1206C683KARACT U]
620 pF [C2220C621KBGAC TU]	68 nF [C0603C683K3RACT U]	68 nF [C0805C683M5UAC TU]	68 nF [C1206C683M5UAC TU]
620 pF [C2225C621KBGAC TU]	68 nF [C0603C683K4RACT U]	68 nF [C0805F683K3RACT U]	68 nF [C1206F683K1RACT U]
640455-5 640455-8	68 nF [C0603C683K5RACT U]	68 nF [C0805F683K4RACT U]	68 nF [C1206F683K3RACT U]
68 mF [C0402C689K8GACT U]	68 nF [C0603C683K8RACT U]	68 nF [C0805F683K5RACT U]	68 nF [C1206F683K4RACT U]
68 mF [C0805C689KBGAC TU]	68 nF [C0603C683K9RACT U]	68 nF [C1206C683K1RACT U]	68 nF [C1206F683K5RACT U]
68 mF [C1206C689K2GACT U]	68 nF [C0603C683M3VAC TU]	68 nF [C1206C683K2RACT U]	68 nF [C1210C683K1GACT U]
68 nF [C0402C683K4RACT U]	68 nF [C0805C683K1RACT U]	68 nF [C1206C683K3GACT U]	68 nF [C1210C683K1HACT U]
68 nF [C0402C683K8PACT U]	68 nF [C0805C683K3RACT U]	68 nF [C1206C683K3HACT U]	68 nF [C1210C683K1RACT U]
68 nF [C0402C683K8RACT U]	68 nF [C0805C683K4RACT U]	68 nF [C1206C683K5HACT U]	68 nF [C1210C683K2RACT U]
68 nF [C0402C683K9PACT U]	68 nF [C0805C683K5RACT U]	68 nF [C1206C683K5RACT U]	68 nF [C1210C683K3GACT U]

Multisim 14.0 Power Pro Components

68 nF [C1210C683K3HACT U]	68 nF [C1812C683K5HACT U]	68 pF [C0603C680K2GACT U]	68 pF [C1206C680KBGAC TU]
68 nF [C1210C683K5GACT U]	68 nF [C1812C683K5RACT U]	68 pF [C0603C680K3GACT U]	68 pF [C1206C680KDGAC TU]
68 nF [C1210C683K5HACT U]	68 nF [C2220C683K1GACT U]	68 pF [C0603C680K4GACT U]	68 pF [C1206C680KGGAC TU]
68 nF [C1210C683K5RACT U]	68 nF [C2220C683K2GACT U]	68 pF [C0603C680K5GACT U]	68 pF [C1210C680KBGAC TU]
68 nF [C1210C683KARACT U]	68 nF [C2220C683K5GACT U]	68 pF [C0805C680K1GACT U]	68 pF [C1812C680KBGAC TU]
68 nF [C1210F683K2RACT U]	68 nF [CA064C683K4RACT U]	68 pF [C0805C680K2GACT U]	68 pF [C1825C680KBGAC TU]
68 nF [C1812C683K1GACT U]	68 nF [CDR05BX683BKSM]	68 pF [C0805C680K5GACT U]	68 pF [C2220C680KBGAC TU]
68 nF [C1812C683K1HACT U]	68 pF [C0201C680K3GACT U]	68 pF [C0805C680KBGAC TU]	68 pF [C2225C680KBGAC TU]
68 nF [C1812C683K1RACT U]	68 pF [C0402C680K3GACT U]	68 pF [C1206C680K1GACT U]	68 pF [CA064C680K5GAC TU]
68 nF [C1812C683K2RACT U]	68 pF [C0402C680K5GACT U]	68 pF [C1206C680K2GACT U]	68 pF [CA064C680K8GAC TU]
68 nF [C1812C683K5GACT U]	68 pF [C0402C680K8GACT U]	68 pF [C1206C680K5GACT U]	68 pF [CDR01BP680BKSM]

Multisim 14.0 Power Pro Components

68 uF [A700D686M008AT E015]	68 uF [T491B686M010AT]	68 uF [T491U686M006AT]	68 uF [T494D686M004AT]
68 uF [A700D686M008AT E018]	68 uF [T491C686M004AT]	68 uF [T491U686M010AT]	68 uF [T494D686M006AT]
68 uF [A700D686M010AT E015]	68 uF [T491C686M006AT]	68 uF [T491V686M010AT]	68 uF [T494D686M010AT]
68 uF [A700D686M010AT E018]	68 uF [T491C686M016AT]	68 uF [T491V686M016AT]	68 uF [T494D686M016AT]
68 uF [A700V686M006AT E018]	68 uF [T491D686M004AT]	68 uF [T491X686M020AT]	68 uF [T494D686M020AT]
68 uF [A700V686M006AT E025]	68 uF [T491D686M006AT]	68 uF [T491X686M025AT]	68 uF [T494D686M025AT]
68 uF [A700V686M006AT E028]	68 uF [T491D686M010AT]	68 uF [T494A686M004AT]	68 uF [T494D686M025AT]
68 uF [T419G686M010AH 4250]	68 uF [T491D686M016AT]	68 uF [T494A686M006AT]	68 uF [T494U686M004AT]
68 uF [T491A686M004AT]	68 uF [T491D686M020AT]	68 uF [T494B686M004AT]	68 uF [T494U686M006AT]
68 uF [T491A686M006AT]	68 uF [T491D686M025AT]	68 uF [T494B686M006AT]	68 uF [T494U686M010AT]
68 uF [T491B686M004AT]	68 uF [T491U686M004AT]	68 uF [T494C686M004AT]	68 uF [T494V686M010AT]
68 uF [T491B686M006AT]		68 uF [T494C686M006AT]	68 uF [T494V686M016AT]
		68 uF [T494C686M010AT]	68 uF [T494X686M020AT]
		68 uF [T494C686M016AT]	

Multisim 14.0 Power Pro Components

68 uF [T494X686M025AT]	68 uF [T495D686M020AT E150]	68 uF [T520A686M006AT E150]	68 uF [T520C686M006AT E100]
68 uF [T495B686M010AT E900]	68 uF [T495D686M025AT E150]	68 uF [T520A686M2R5AT E070]	68 uF [T520C686M010AT E045]
68 uF [T495C686M010AT E225]	68 uF [T495D686M025AT E200]	68 uF [T520A686M2R5AT E080]	68 uF [T520T686M004AT E070]
68 uF [T495D686M006AT E175]	68 uF [T495V686M010AT E100]	68 uF [T520B686M004AT E025]	68 uF [T520T686M006AT E070]
68 uF [T495D686M010AT E070]	68 uF [T495V686M010AT E140]	68 uF [T520B686M004AT E035]	68 uF [T520T686M006AT E150]
68 uF [T495D686M010AT E090]	68 uF [T495V686M016AT E300]	68 uF [T520B686M004AT E040]	68 uF [T520U686M004AT E055]
68 uF [T495D686M010AT E150]	68 uF [T495X686M010AT E150]	68 uF [T520B686M004AT E070]	68 uF [T520U686M006AT E055]
68 uF [T495D686M016AT E070]	68 uF [T495X686M020AT E150]	68 uF [T520B686M006AT E025]	68 uF [T520U686M006AT E070]
68 uF [T495D686M016AT E100]	68 uF [T495X686M025AT E125]	68 uF [T520B686M006AT E035]	68 uF [T520V686M010AT E025]
68 uF [T495D686M016AT E150]	68 uF [T495X686M025AT E200]	68 uF [T520B686M006AT E040]	68 uF [T520V686M010AT E040]
68 uF [T495D686M020AT E070]	68 uF [T513X686M025AH 6110]	68 uF [T520B686M006AT E070]	68 uF [T520V686M010AT E045]

Multisim 14.0 Power Pro Components

68 uF [T520V686M010AT E060]	680 nF [C0603C684K8PACT U]	680 nF [C1206F684K4RACT U]	680 nF [C1812F684K1RACT U]
68 uF [T520V686M010AT E100]	680 nF [C0805C684K3PACT U]	680 nF [C1210C684K3RACT U]	680 nF [C1812F684K3RACT U]
68 uF [T520W686M010AT E040]	680 nF [C0805C684K4RACT U]	680 nF [C1210C684K4RACT U]	680 nF [C1812F684K5RACT U]
68 uF [T521D686M016AT E050]	680 nF [C0805C684K8RACT U]	680 nF [C1210C684K5RACT U]	680 nF [C1825C684K1RACT U]
68 uF [T521V686M016AT E050]	680 nF [C0805C684M4VAC TU]	680 nF [C1210C684M3VAC TU]	680 nF [C1825C684K5RACT U]
68 uF [T521V686M016AT E090]	680 nF [C1206C684K3RACT U]	680 nF [C1210C684M5VAC TU]	680 nF [C1825C684KARACT U]
68 uF [T525B686M004AT E080]	680 nF [C1206C684K4RACT U]	680 nF [C1210F684K3RACT U]	680 nF [C2220C684K1RACT U]
68 uF [T525B686M006AT E080]	680 nF [C1206C684K5RACT U]	680 nF [C1210F684K4RACT U]	680 nF [C2220C684K5RACT U]
68 uF [T525T686M004AT E080]	680 nF [C1206C684K8RACT U]	680 nF [C1210F684K5RACT U]	680 nF [C2220C684KARACT U]
68 uF [T543U686M006AT E055]	680 nF [C1206C684M3VAC TU]	680 nF [C1812C684K5RACT U]	680 nF [C2225C684K1RACT U]
680 nF [C0603C684K4PACT U]	680 nF [C1206C684M4VAC TU]	680 nF [C1812C684M5UAC TU]	680 nF [C2225C684K5RACT U]

Multisim 14.0 Power Pro Components

680 nF [C2225C684KARACT U]	680 pF [C0402C681K1HACT U]	680 pF [C0603C681K3HACT U]	680 pF [C0805C681K5GACT U]
680 nF [T491A684M020AT]	680 pF [C0402C681K3GACT U]	680 pF [C0603C681K3RACT U]	680 pF [C0805C681K5RACT U]
680 nF [T491A684M025AT]	680 pF [C0402C681K3HACT U]	680 pF [C0603C681K4RACT U]	680 pF [C1206C681K1GACT U]
680 nF [T491A684M035AT]	680 pF [C0402C681K3RACT U]	680 pF [C0603C681K5GACT U]	680 pF [C1206C681K2GACT U]
680 nF [T491B684M035AT]	680 pF [C0402C681K4RACT U]	680 pF [C0603C681K5HACT U]	680 pF [C1206C681K5GACT U]
680 nF [T491B684M050AT]	680 pF [C0402C681K5HACT U]	680 pF [C0603C681K5RACT U]	680 pF [C1206C681KCGAC TU]
680 nF [T491C684M050AT]	680 pF [C0402C681K5RACT U]	680 pF [C0805C681K1GACT U]	680 pF [C1210C681KBGAC TU]
680 nF [T494A684M020AT]	680 pF [C0603C681K1HACT U]	680 pF [C0805C681K1RACT U]	680 pF [C1210C681KCGAC TU]
680 nF [T494A684M025AT]	680 pF [C0603C681K1RACT U]	680 pF [C0805C681K2RACT U]	680 pF [C1210C681KDGAC TU]
680 nF [T494A684M035AT]	680 pF [C0603C681K2RACT U]	680 pF [C0805C681K4GACT U]	680 pF [C1812C681KBGAC TU]
680 nF [T494B684M035AT]	680 pF [C0603C681K3GACT U]	680 pF [C0805C681K4RACT U]	680 pF [C1825C681KBGAC TU]
680 nF [T494B684M050AT]			
680 nF [T496C684M050AT 6110]			

Multisim 14.0 Power Pro Components

680 pF [C2220C681KBGAC TU]	680 uF [T510X687M006AT E023]	680 uF [T520D687M2R5AT E010]	680 uF [T525D687M003AT E025]
680 pF [C2220C681KZGACT U]	680 uF [T513E687M006AH 6110]	680 uF [T520D687M2R5AT E015]	680 uF [T525D687M2R5AT E025]
680 pF [C2225C681KBGAC TU]	680 uF [T513E687M006AH 6120]	680 uF [T520D687M2R5AT E040]	680 uF [T530D687M003AT E010]
680 uF [T491D687M004AT]	680 uF [T513X687M004AH 6110]	680 uF [T520X687M004AT E010]	680 uF [T530D687M2R5AT E006]
680 uF [T491E687M006AT]	680 uF [T513X687M006AH 6110]	680 uF [T520X687M004AT E015]	680 uF [T530D687M2R5AT E010]
680 uF [T491X687M004AT]	680 uF [T513X687M006AH 6120]	680 uF [T520X687M004AT E035]	680 uF [T530X687M004AT E004]
680 uF [T494D687M004AT]	680 uF [T520D687M003AT E015]	680 uF [T520Y687M004AT E010]	680 uF [T530X687M004AT E006]
680 uF [T494E687M006AT]	680 uF [T520D687M003AT E040]	680 uF [T520Y687M004AT E015]	680 uF [T530X687M004AT E010]
680 uF [T494X687M004AT]	680 uF [T520D687M004AT E012]	680 uF [T520Y687M004AT E025]	680 uF [T530X687M006AT E010]
680 uF [T510E687M006AT E012]	680 uF [T520D687M004AT E015]	680 uF [T520Y687M2R5AT E015]	680 uF [T530X687M006AT E018]
680 uF [T510E687M006AT E023]	680 uF [T520D687M004AT E025]	680 uF [T520Y687M2R5AT E025]	680 uF [T530Y687M004AT E005]

Multisim 14.0 Power Pro Components

680 uF [T530Y687M2R5AT E006]	6N136-X009T	7.5 nF [C0805C752K1HACT U]	7406N
	6N136-X016		7407N
680 uF [T543X687M004AT E015]	6N136-X017T	7.5 nF	7408J
	6N136-X019T	[C0805C752K3HACT U]	7408N
690-009-521-900	6N137	7.5 nF	7409N
6DJ8	6N137-X006	[C0805C752K5GACT U]	74100J
6F6	6N137-X007T		74100N
6J5	6N139-000E	7.5 nF [C0805C752K5HACT U]	74107N
6L6GC	6N139-020E		74109N
6Line_Bussed	6N139-060E	7.5 nF [C1206C752K1HACT U]	7410N
6Line_Isolated	6N139-300E		74116N
6N1136	6N139-320E	7.5 nF	74125N
6N1136-X006	6N139-360E	[C1206C752K3HACT U]	74126N
6N1136-X009T	6POS_ROTARY	7.5 nF	7412N
6N136	6SF5	[C1206C752K5HACT U]	74132N
6N136-000E	6SL7GT	7.5 nF	74136N
6N136-020E	6SN7GTB	[CDR34BP752AKSM]	7413N
6N136-060E	6STEP_DECODER		74145N
6N136-300E	6TQ045	73391-0060	74147N
6N136-320E	6V6GTA	7400N	74148N
6N136-360E	7.5 nF [C0603C752K3HACT U]	7401N	7414N
6N136-X001		7402N	74150N
6N136-X006	7.5 nF [C0805C752K1GACT U]	7403N	74151N
6N136-X007T		7404N	74152AJ
		7405N	74152AN

Multisim 14.0 Power Pro Components

74153N	74192N	7428N	7443J
74154N	74193N	74290N	7443N
74155N	74194N	74293N	7444J
74156N	74195N	74298N	7444N
74157N	74198N	7430N	7445N
74159N	74199N	74320-1004	7446N
74160N	741-DIV	74320-3004	7447N
74161N	7420N	74320-4004	7448N
74162N	7422N	74320-5000	7451N
74163N	74246N	7432N	7454N
74164N	74247N	7433N	7472N
74165N	74248J	74351N	7473N
74166N	74248N	74365N	7474N
7416N	74249J	74366N	7475N
74173N	74249N	74367N	7476N
74174N	74251J	74368N	7477W
74175N	74251N	7437N	7482J
7417N	74259N	7438N	7482N
74180N	7425N	74390N	7483N
74181J	7426N	74393N	7485N
74181N	74273DW	7439N	7486N
74182J	74273N	7440N	749070-9
74182N	74279N	74425N	7490N
74190N	7427N	74426N	7491N
74191N	74283N	7442N	7492N

Multisim 14.0 Power Pro Components

7493N	74ALS133M	74ALS169N	74ALS273N
74ACT16245DGG	74ALS133N	74ALS174M	74ALS273WM
74ACT16245DL	74ALS137M	74ALS174N	74ALS27M
74ALS00M	74ALS137N	74ALS175M	74ALS27N
74ALS00N	74ALS138M	74ALS175N	74ALS30AM
74ALS02M	74ALS138N	74ALS20AM	74ALS30AN
74ALS02N	74ALS14M	74ALS20AN	74ALS32M
74ALS03BM	74ALS14N	74ALS21AM	74ALS32N
74ALS03BN	74ALS151M	74ALS21AN	74ALS373N
74ALS04BM	74ALS151N	74ALS240AN	74ALS373WM
74ALS04BN	74ALS153M	74ALS240AWM	74ALS374AN
74ALS05AM	74ALS153N	74ALS241AN	74ALS374AWM
74ALS05AN	74ALS157M	74ALS241AWM	74ALS37AM
74ALS08M	74ALS157N	74ALS244AN	74ALS37AN
74ALS08N	74ALS158M	74ALS244AWM	74ALS38AM
74ALS09M	74ALS158N	74ALS245AN	74ALS38AN
74ALS09N	74ALS161BM	74ALS245AWM	74ALS74AM
74ALS109AM	74ALS161BN	74ALS251M	74ALS74AN
74ALS109AN	74ALS162BM	74ALS251N	74ALS86M
74ALS10AM	74ALS162BN	74ALS253M	74ALS86N
74ALS10AN	74ALS163BM	74ALS253N	74AS00M
74ALS11AM	74ALS163BN	74ALS257M	74AS00N
74ALS11AN	74ALS165M	74ALS257N	74AS04M
74ALS125M	74ALS165N	74ALS258M	74AS04N
74ALS125N	74ALS169M	74ALS258N	74AS08M

Multisim 14.0 Power Pro Components

74AS08N	74AS257N	74F04N	74F148D
74AS10M	74AS258M	74F08D	74F148N
74AS10N	74AS258N	74F08N	74F14D
74AS157M	74AS27M	74F109D	74F14N
74AS157N	74AS27N	74F109N	74F151D
74AS158M	74AS280M	74F10D	74F151N
74AS158N	74AS280N	74F10N	74F153D
74AS161M	74AS30M	74F112D	74F153N
74AS161N	74AS30N	74F112N	74F157AD
74AS163M	74AS32M	74F113D	74F157AN
74AS163N	74AS32N	74F113N	74F157D
74AS169AM	74AS34N	74F114D	74F157N
74AS169AN	74AS373N	74F114N	74F158AD
74AS174N	74AS373WM	74F11D	74F158AN
74AS181BN	74AS374N	74F11N	74F158D
74AS181BNT	74AS374WM	74F125D	74F158N
74AS21M	74AS74M	74F125N	74F160AD
74AS21N	74AS74N	74F126D	74F160AN
74AS240N	74AS86M	74F126N	74F161AD
74AS240WM	74AS86N	74F138D	74F161AN
74AS244N	74F00D	74F138N	74F162AD
74AS244WM	74F00N	74F139D	74F162AN
74AS245N	74F02D	74F139N	74F163AD
74AS245WM	74F02N	74F13D	74F163AN
74AS257M	74F04D	74F13N	74F164D

Multisim 14.0 Power Pro Components

74F164N	74F21N	74F273PC	74F373N
74F169D	74F240D	74F273SC	74F374D
74F169N	74F240N	74F27M	74F374N
74F174D	74F241D	74F27N	74F378D
74F174N	74F241N	74F280D	74F378N
74F175D	74F242D	74F280N	74F379D
74F175N	74F242N	74F283D	74F379N
74F181N	74F243D	74F283N	74F37D
74F182D	74F243N	74F32D	74F37N
74F182N	74F244D	74F32N	74F38D
74F190D	74F244N	74F350D	74F38N
74F190N	74F245D	74F350N	74F399D
74F191D	74F245N	74F352D	74F399N
74F191N	74F251D	74F352N	74F40D
74F192D	74F251N	74F353D	74F40N
74F192N	74F253D	74F353N	74F51D
74F193D	74F253N	74F365D	74F51N
74F193N	74F257D	74F365N	74F521DW
74F194D	74F257N	74F366D	74F521N
74F194N	74F258AD	74F366N	74F533PC
74F195D	74F258AN	74F367D	74F533SC
74F195N	74F258D	74F367N	74F534PC
74F20D	74F258N	74F368D	74F534SC
74F20N	74F259D	74F368N	74F540PC
74F21D	74F259N	74F373D	74F540SC

Multisim 14.0 Power Pro Components

74F541PC	74F828SPC	74HC03D_6V	74HC09N_2V
74F541SC	74F85D	74HC03N_2V	74HC09N_4V
74F563PC	74F85N	74HC03N_4V	74HC09N_6V
74F563SC	74F86D	74HC03N_6V	74HC107D_2V
74F564PC	74F86N	74HC04D_2V	74HC107D_4V
74F564SC	74HC00D_2V	74HC04D_4V	74HC107D_6V
74F573PC	74HC00D_4V	74HC04D_6V	74HC107N_2V
74F573SC	74HC00D_6V	74HC04N_2V	74HC107N_4V
74F574PC	74HC00N_2V	74HC04N_4V	74HC107N_6V
74F574SC	74HC00N_4V	74HC04N_6V	74HC109D_2V
74F640PC	74HC00N_6V	74HC05D_2V	74HC109D_4V
74F640SC	74HC01D_2V	74HC05D_4V	74HC109D_6V
74F645PC	74HC01D_4V	74HC05D_6V	74HC109N_2V
74F645SC	74HC01D_6V	74HC05N_2V	74HC109N_4V
74F74D	74HC01N_2V	74HC05N_4V	74HC109N_6V
74F74N	74HC01N_4V	74HC05N_6V	74HC10D_2V
74F821PC	74HC01N_6V	74HC08D_2V	74HC10D_4V
74F821SPC	74HC02D_2V	74HC08D_4V	74HC10D_6V
74F823PC	74HC02D_4V	74HC08D_6V	74HC10N_2V
74F823SPC	74HC02D_6V	74HC08N_2V	74HC10N_4V
74F825PC	74HC02N_2V	74HC08N_4V	74HC10N_6V
74F825SPC	74HC02N_4V	74HC08N_6V	74HC112D_2V
74F827PC	74HC02N_6V	74HC09D_2V	74HC112D_4V
74F827SPC	74HC03D_2V	74HC09D_4V	74HC112D_6V
74F828PC	74HC03D_4V	74HC09D_6V	74HC112N_2V

Multisim 14.0 Power Pro Components

74HC112N_4V	74HC126N_6V	74HC139N_2V	74HC152D_4V
74HC112N_6V	74HC133D_2V	74HC139N_4V	74HC152D_6V
74HC113D_2V	74HC133D_4V	74HC139N_6V	74HC152N_2V
74HC113D_4V	74HC133D_4V	74HC147N_2V	74HC152N_4V
74HC113D_6V	74HC133D_6V	74HC147N_4V	74HC152N_6V
74HC113N_2V	74HC133N_2V	74HC147N_6V	74HC153D_2V
74HC113N_4V	74HC133N_4V	74HC148DW_2V	74HC153D_4V
74HC113N_6V	74HC133N_6V	74HC148DW_4V	74HC153D_6V
74HC114D_2V	74HC137D_2V	74HC148DW_6V	74HC153DW_2V
74HC114D_4V	74HC137D_4V	74HC148N_2V	74HC153DW_4V
74HC114D_6V	74HC137D_6V	74HC148N_4V	74HC153DW_6V
74HC114N_2V	74HC137N_2V	74HC148N_6V	74HC153N_2V
74HC114N_4V	74HC137N_4V	74HC14D_2V	74HC153N_4V
74HC114N_6V	74HC137N_6V	74HC14D_4V	74HC153N_6V
74HC11D_2V	74HC138D_2V	74HC14D_6V	74HC154DW_2V
74HC11D_4V	74HC138D_4V	74HC14N_2V	74HC154DW_4V
74HC11D_6V	74HC138D_4V	74HC14N_4V	74HC154DW_6V
74HC11N_2V	74HC138D_6V	74HC14N_6V	74HC154NT_2V
74HC11N_4V	74HC138N_2V	74HC151D_2V	74HC154NT_4V
74HC11N_6V	74HC138N_4V	74HC151D_4V	74HC154NT_6V
74HC125N_2V	74HC138N_4V	74HC151D_6V	74HC157D_2V
74HC125N_4V	74HC138N_6V	74HC151N_2V	74HC157D_4V
74HC125N_6V	74HC139DW_2V	74HC151N_4V	74HC157D_6V
74HC126N_2V	74HC139DW_4V	74HC151N_6V	74HC157N_2V
74HC126N_4V	74HC139DW_6V	74HC152D_2V	74HC157N_4V

Multisim 14.0 Power Pro Components

74HC157N_6V	74HC163D_2V	74HC173N_4V	74HC190N_6V
74HC158D_2V	74HC163D_4V	74HC173N_6V	74HC191D_2V
74HC158D_4V	74HC163D_6V	74HC174D_2V	74HC191D_4V
74HC158D_6V	74HC163N_2V	74HC174D_4V	74HC191D_6V
74HC158N_2V	74HC163N_4V	74HC174D_6V	74HC191N_2V
74HC158N_4V	74HC163N_6V	74HC174N_2V	74HC191N_4V
74HC158N_6V	74HC164N_2V	74HC174N_4V	74HC191N_6V
74HC160D_2V	74HC164N_4V	74HC174N_6V	74HC192D_2V
74HC160D_4V	74HC164N_6V	74HC175D_2V	74HC192D_4V
74HC160D_6V	74HC165D_2V	74HC175D_4V	74HC192D_6V
74HC160N_2V	74HC165D_4V	74HC175D_6V	74HC192N_2V
74HC160N_4V	74HC165D_6V	74HC175N_2V	74HC192N_4V
74HC160N_6V	74HC165N_2V	74HC175N_4V	74HC192N_6V
74HC161D_2V	74HC165N_4V	74HC175N_6V	74HC193D_2V
74HC161D_4V	74HC165N_6V	74HC180D_2V	74HC193D_4V
74HC161D_6V	74HC166D_2V	74HC180D_4V	74HC193D_6V
74HC161N_2V	74HC166D_4V	74HC180D_6V	74HC193N_2V
74HC161N_4V	74HC166D_6V	74HC180N_2V	74HC193N_4V
74HC161N_6V	74HC166N_2V	74HC180N_4V	74HC193N_6V
74HC162D_2V	74HC166N_4V	74HC180N_6V	74HC194N_2V
74HC162D_4V	74HC166N_6V	74HC190D_2V	74HC194N_4V
74HC162D_6V	74HC173D_2V	74HC190D_4V	74HC194N_6V
74HC162N_2V	74HC173D_4V	74HC190D_6V	74HC195N_2V
74HC162N_4V	74HC173D_6V	74HC190N_2V	74HC195N_4V
74HC162N_6V	74HC173N_2V	74HC190N_4V	74HC195N_6V

Multisim 14.0 Power Pro Components

74HC20D_2V	74HC242N_4V	74HC253D_4V	74HC266D_6V
74HC20D_4V	74HC242N_6V	74HC253D_6V	74HC266N_2V
74HC20D_6V	74HC243N_2V	74HC253N_2V	74HC266N_4V
74HC20N_2V	74HC243N_4V	74HC253N_4V	74HC266N_6V
74HC20N_4V	74HC243N_6V	74HC253N_6V	74HC273DW_2V
74HC20N_6V	74HC244_4V	74HC257D_2V	74HC273DW_4V
74HC21D_2V	74HC244DW_2V	74HC257D_4V	74HC273DW_6V
74HC21D_4V	74HC244DW_4V	74HC257D_6V	74HC273N_2V
74HC21D_6V	74HC244DW_6V	74HC257N_2V	74HC273N_4V
74HC21N_2V	74HC244N_2V	74HC257N_4V	74HC273N_6V
74HC21N_4V	74HC244N_4V	74HC257N_6V	74HC27D_2V
74HC21N_6V	74HC244N_6V	74HC258D_2V	74HC27D_4V
74HC240DW_2V	74HC245DW_2V	74HC258D_4V	74HC27D_6V
74HC240DW_4V	74HC245DW_4V	74HC258D_6V	74HC27N_2V
74HC240DW_6V	74HC245DW_6V	74HC258N_2V	74HC27N_4V
74HC240N_2V	74HC245N_2V	74HC258N_4V	74HC27N_6V
74HC240N_4V	74HC245N_4V	74HC258N_6V	74HC280D_2V
74HC240N_6V	74HC245N_6V	74HC259D_2V	74HC280D_4V
74HC241DW_2V	74HC251D_2V	74HC259D_4V	74HC280D_6V
74HC241DW_4V	74HC251D_4V	74HC259D_6V	74HC280N_2V
74HC241DW_6V	74HC251D_6V	74HC259N_2V	74HC280N_4V
74HC241N_2V	74HC251N_2V	74HC259N_4V	74HC280N_6V
74HC241N_4V	74HC251N_4V	74HC259N_6V	74HC283D_2V
74HC241N_6V	74HC251N_6V	74HC266D_2V	74HC283D_4V
74HC242N_2V	74HC253D_2V	74HC266D_4V	74HC283D_6V

Multisim 14.0 Power Pro Components

74HC283N_2V	74HC366D_4V	74HC373DW_6V	74HC378N_2V
74HC283N_4V	74HC366D_6V	74HC373N_2V	74HC378N_4V
74HC283N_6V	74HC366N_2V	74HC373N_4V	74HC378N_6V
74HC298N_2V	74HC366N_4V	74HC373N_6V	74HC379D_2V
74HC298N_4V	74HC366N_6V	74HC374DW_2V	74HC379D_4V
74HC298N_6V	74HC367D_2V	74HC374DW_4V	74HC379D_6V
74HC30D_2V	74HC367D_4V	74HC374DW_6V	74HC379J_2V
74HC30D_4V	74HC367D_6V	74HC374N_2V	74HC379J_4V
74HC30D_6V	74HC367N_2V	74HC374N_4V	74HC379J_6V
74HC30N_2V	74HC367N_4V	74HC374N_6V	74HC379N_2V
74HC30N_4V	74HC367N_6V	74HC375D_2V	74HC379N_4V
74HC30N_6V	74HC368D_2V	74HC375D_4V	74HC379N_6V
74HC32D_2V	74HC368D_4V	74HC375D_6V	74HC386D_2V
74HC32D_4V	74HC368D_6V	74HC375N_2V	74HC386D_4V
74HC32D_6V	74HC368N_2V	74HC375N_4V	74HC386D_6V
74HC32N_2V	74HC368N_4V	74HC375N_6V	74HC386N_2V
74HC32N_4V	74HC368N_6V	74HC377DW_2V	74HC386N_4V
74HC32N_6V	74HC36D_2V	74HC377DW_4V	74HC386N_6V
74HC365D_2V	74HC36D_4V	74HC377DW_6V	74HC390D_2V
74HC365D_4V	74HC36D_6V	74HC377N_2V	74HC390D_4V
74HC365D_6V	74HC36N_2V	74HC377N_4V	74HC390D_6V
74HC365N_2V	74HC36N_4V	74HC377N_6V	74HC390N_2V
74HC365N_4V	74HC36N_6V	74HC378D_2V	74HC390N_4V
74HC365N_6V	74HC373DW_2V	74HC378D_4V	74HC390N_6V
74HC366D_2V	74HC373DW_4V	74HC378D_6V	74HC393N_2V

Multisim 14.0 Power Pro Components

74HC393N_4V	74HC74N_6V	74HC85AD_2V	74LS03N
74HC393N_6V	74HC75D_2V	74HC85AD_4V	74LS04D
74HC42D_2V	74HC75D_4V	74HC85AD_6V	74LS04D
74HC42D_4V	74HC75D_6V	74HC85AN_2V	74LS04N
74HC42D_6V	74HC75N_2V	74HC85AN_4V	74LS04N
74HC42N_2V	74HC75N_4V	74HC85AN_6V	74LS05D
74HC42N_4V	74HC75N_6V	74HC86D_2V	74LS05D
74HC42N_6V	74HC76D_2V	74HC86D_4V	74LS05N
74HC51D_2V	74HC76D_4V	74HC86D_6V	74LS05N
74HC51D_4V	74HC76D_6V	74HC86N_2V	74LS08D
74HC51D_6V	74HC76N_2V	74HC86N_4V	74LS08D
74HC51N_2V	74HC76N_4V	74HC86N_6V	74LS08J
74HC51N_4V	74HC76N_6V	74LS00D	74LS08J
74HC51N_6V	74HC77D_2V	74LS00D	74LS08N
74HC73D_2V	74HC77D_4V	74LS00N	74LS08N
74HC73D_4V	74HC77D_6V	74LS00N	74LS09D
74HC73D_6V	74HC77N_2V	74LS01D	74LS09D
74HC73N_2V	74HC77N_4V	74LS01N	74LS09N
74HC73N_4V	74HC77N_6V	74LS02D	74LS09N
74HC73N_6V	74HC78D_2V	74LS02D	74LS107D
74HC74D_2V	74HC78D_4V	74LS02N	74LS107D
74HC74D_4V	74HC78D_6V	74LS02N	74LS107N
74HC74D_6V	74HC78N_2V	74LS03D	74LS107N
74HC74N_2V	74HC78N_4V	74LS03D	74LS109D
74HC74N_4V	74HC78N_6V	74LS03N	74LS109D

Multisim 14.0 Power Pro Components

74LS109N	74LS126D	74LS145D	74LS153N
74LS109N	74LS126D	74LS145D	74LS155D
74LS10D	74LS126N	74LS145N	74LS155D
74LS10D	74LS12D	74LS145N	74LS155N
74LS10N	74LS12D	74LS147D	74LS155N
74LS10N	74LS12N	74LS147D	74LS156D
74LS112D	74LS12N	74LS147N	74LS156D
74LS112D	74LS132D	74LS147N	74LS156N
74LS112N	74LS132D	74LS148D	74LS156N
74LS112N	74LS132N	74LS148D	74LS157D
74LS113D	74LS132N	74LS148N	74LS157D
74LS113D	74LS136D	74LS148N	74LS157N
74LS113N	74LS136N	74LS14D	74LS157N
74LS113N	74LS137D	74LS14D	74LS158D
74LS114D	74LS137N	74LS14N	74LS158D
74LS114D	74LS138D	74LS14N	74LS158N
74LS114N	74LS138D	74LS151D	74LS158N
74LS114N	74LS138N	74LS151D	74LS15D
74LS11D	74LS138N	74LS151N	74LS15D
74LS11D	74LS139D	74LS151N	74LS15N
74LS11N	74LS139D	74LS152J	74LS15N
74LS11N	74LS139N	74LS152N	74LS160D
74LS125D	74LS139N	74LS153D	74LS160D
74LS125D	74LS13D	74LS153D	74LS160N
74LS125N	74LS13N	74LS153N	74LS160N

Multisim 14.0 Power Pro Components

74LS161D	74LS169N	74LS191N	74LS21N
74LS161N	74LS173D	74LS191N	74LS22D
74LS162D	74LS173D	74LS192D	74LS22D
74LS162D	74LS173N	74LS192D	74LS22N
74LS162N	74LS173N	74LS192N	74LS22N
74LS162N	74LS174D	74LS192N	74LS240DW
74LS163D	74LS174D	74LS193D	74LS240DW
74LS163D	74LS174N	74LS193N	74LS240N
74LS163N	74LS174N	74LS194D	74LS240N
74LS163N	74LS175D	74LS194D	74LS241DW
74LS164D	74LS175D	74LS194N	74LS241DW
74LS164D	74LS175N	74LS194N	74LS241N
74LS164N	74LS175N	74LS195D	74LS241N
74LS164N	74LS181DW	74LS195D	74LS242D
74LS165D	74LS181DW	74LS195N	74LS242N
74LS165D	74LS181N	74LS195N	74LS243D
74LS165N	74LS181N	74LS19AD	74LS243N
74LS165N	74LS183D	74LS19AN	74LS244DW
74LS166D	74LS183N	74LS20D	74LS244N
74LS166D	74LS190D	74LS20D	74LS245DW
74LS166N	74LS190D	74LS20N	74LS245N
74LS166N	74LS190N	74LS20N	74LS247D
74LS169D	74LS190N	74LS21D	74LS247N
74LS169D	74LS191D	74LS21D	74LS248D
74LS169N	74LS191D	74LS21N	74LS248N

Multisim 14.0 Power Pro Components

74LS249J	74LS266N	74LS290D	74LS352D
74LS249N	74LS26D	74LS290D	74LS352D
74LS24AD	74LS26D	74LS290N	74LS352N
74LS24AN	74LS26N	74LS290N	74LS352N
74LS251D	74LS26N	74LS293D	74LS353D
74LS251D	74LS273DW	74LS293D	74LS353D
74LS251N	74LS273DW	74LS293N	74LS353N
74LS251N	74LS273N	74LS293N	74LS363D
74LS253D	74LS273N	74LS298D	74LS363N
74LS253D	74LS279D	74LS298D	74LS364D
74LS253N	74LS279N	74LS298N	74LS364N
74LS253N	74LS27D	74LS298N	74LS365D
74LS257D	74LS27D	74LS30D	74LS365D
74LS257D	74LS27N	74LS30N	74LS365N
74LS257N	74LS27N	74LS30N	74LS365N
74LS257N	74LS280D	74LS32D	74LS366D
74LS258D	74LS280D	74LS32D	74LS366N
74LS258D	74LS280N	74LS32N	74LS367D
74LS258N	74LS280N	74LS32N	74LS367D
74LS258N	74LS283D	74LS33D	74LS367N
74LS259D	74LS283N	74LS33D	74LS367N
74LS259N	74LS28D	74LS33N	74LS368D
74LS266D	74LS28D	74LS33N	74LS368D
74LS266D	74LS28N	74LS348D	74LS368N
74LS266N	74LS28N	74LS348N	74LS368N

Multisim 14.0 Power Pro Components

74LS373DW	74LS386D	74LS42N	74LS49D
74LS373DW	74LS386N	74LS445D	74LS49N
74LS373N	74LS38D	74LS445D	74LS51D
74LS373N	74LS38D	74LS445N	74LS51D
74LS374DW	74LS38N	74LS445N	74LS51N
74LS374DW	74LS38N	74LS465DW	74LS51N
74LS374N	74LS390D	74LS465DW	74LS540DW
74LS374N	74LS390N	74LS465N	74LS540N
74LS375D	74LS393D	74LS465N	74LS541DW
74LS375N	74LS393D	74LS466DW	74LS541N
74LS377DW	74LS393N	74LS466DW	74LS54D
74LS377DW	74LS393N	74LS466N	74LS54D
74LS377N	74LS395D	74LS466N	74LS54N
74LS377N	74LS395D	74LS467DW	74LS54N
74LS378D	74LS395N	74LS467N	74LS55D
74LS378D	74LS395N	74LS468DW	74LS55D
74LS378N	74LS399D	74LS468N	74LS55N
74LS378N	74LS399N	74LS47D	74LS55N
74LS379D	74LS40D	74LS47D	74LS640DW
74LS379D	74LS40D	74LS47N	74LS640N
74LS379N	74LS40N	74LS47N	74LS645DW
74LS379N	74LS40N	74LS48D	74LS645N
74LS37D	74LS42D	74LS48D	74LS69D
74LS37D	74LS42D	74LS48N	74LS69D
74LS37N	74LS42N	74LS48N	74LS69N

Multisim 14.0 Power Pro Components

74LS69N	74LS85D	74S02N	74S133N
74LS73D	74LS85N	74S03D	74S134D
74LS73D	74LS86D	74S03N	74S134D
74LS73N	74LS86D	74S04D	74S134N
74LS73N	74LS86N	74S04N	74S135D
74LS74D	74LS86N	74S05D	74S135N
74LS74D	74LS90D	74S05N	74S138D
74LS74N	74LS90D	74S08D	74S138N
74LS74N	74LS90N	74S08J	74S139D
74LS75D	74LS90N	74S08N	74S139N
74LS75D	74LS91D	74S09D	74S151D
74LS75N	74LS91D	74S09N	74S151N
74LS75N	74LS91N	74S10D	74S153D
74LS76D	74LS91N	74S10N	74S153N
74LS76D	74LS92D	74S112D	74S157D
74LS76N	74LS92D	74S112N	74S157N
74LS76N	74LS92N	74S113D	74S158D
74LS77W	74LS92N	74S113N	74S158N
74LS77W	74LS93D	74S114D	74S15D
74LS78D	74LS93D	74S114N	74S15N
74LS78D	74LS93N	74S11D	74S162D
74LS78N	74LS93N	74S11N	74S162N
74LS78N	74S00D	74S132D	74S163D
74LS83D	74S00N	74S132N	74S163N
74LS83N	74S02D	74S133D	74S169D

Multisim 14.0 Power Pro Components

74S169N	74S253D	74S40N	75 pF [C0603C750K5GACT U]
74S174D	74S253N	74S51D	
74S174N	74S257D	74S51N	75 pF [C0805C750K2GACT U]
74S175D	74S257N	74S74D	
74S175N	74S258D	74S74N	75 pF [C0805C750KBGAC TU]
74S181DW	74S258N	74S85D	
74S181N	74S280D	74S85N	75 pF [C0805C750KCGAC TU]
74S182D	74S280N	74S86D	
74S182N	74S283D	74S86N	75 pF [C1206C750K5GACT U]
74S194D	74S283N	74STD06N	
74S194N	74S30D	74STD07N	75 pF [C1206C750KBGAC TU]
74S195D	74S30N	74STD116N	
74S195N	74S32D	74STD150N	75 pF [C1210C750KBGAC TU]
74S20D	74S32N	74STD154N	
74S20N	74S350D	74STD159N	75 pF [C1812C750KBGAC TU]
74S22D	74S350N	74STD16N	
74S22N	74S373DW	74STD17N	75 pF [C1825C750KBGAC TU]
74S240DW	74S373N	74STD198N	
74S240N	74S374DW	74STD199N	75 pF [C2220C750KBGAC TU]
74S241DW	74S374N	74STD25N	
74S241N	74S37D	74STD39N	75 pF [C2225C750KBGAC TU]
74S244DW	74S37N	74STD45N	
74S244N	74S38D	74STD72N	75 pF [C0805C759KBGAC TU]
74S251D	74S38N	75 mF [C0805C759KBGAC TU]	
74S251N	74S40D		

Multisim 14.0 Power Pro Components

750 pF [C0402C751K1HACT U]	750 pF [C2225C751KBGAC TU]	8.2 nF [C0603C822K3GACT U]	8.2 nF [C0805C822K3RACT U]
750 pF [C0402C751K3HACT U]	75LQ150 75SLQ030	8.2 nF [C0603C822K3HACT U]	8.2 nF [C0805C822K4RACT U]
750 pF [C0402C751K5HACT U]	75SLQ045 75SLQ060	8.2 nF [C0603C822K3RACT U]	8.2 nF [C0805C822K5GACT U]
750 pF [C0603C751K1HACT U]	777778-01 777779-01	8.2 nF [C0603C822K4RACT U]	8.2 nF [C0805C822K5HACT U]
750 pF [C0603C751K3HACT U]	779157-01 781334-01	8.2 nF [C0603C822K5RACT U]	8.2 nF [C0805C822K5RACT U]
750 pF [C0603C751K5GACT U]	7Line_Bussed 7Line_Isolated	8.2 nF [C0805C822K1GACT U]	8.2 nF [C1206C822K1HACT U]
750 pF [C0603C751K5HACT U]	7POS_ROTARY 8.2 nF [C0402C822K3RACT U]	8.2 nF [C0805C822K1HACT U]	8.2 nF [C1206C822K1RACT U]
750 pF [C1210C751KBGAC TU]	8.2 nF [C0402C822K4RACT U]	8.2 nF [C0805C822K1RACT U]	8.2 nF [C1206C822K2RACT U]
750 pF [C1812C751KBGAC TU]	8.2 nF [C0402C822K5RACT U]	8.2 nF [C0805C822K2RACT U]	8.2 nF [C1206C822K3HACT U]
750 pF [C1825C751KBGAC TU]	8.2 nF [C0402C822K9RACT U]	8.2 nF [C0805C822K3GACT U]	8.2 nF [C1206C822K5HACT U]
750 pF [C2220C751KBGAC TU]	8.2 nF [C0603C822K1RACT U]	8.2 nF [C0805C822K3HACT U]	8.2 nF [C1206C822K5RACT U]

Multisim 14.0 Power Pro Components

8.2 nF [C1206C822KARACT U]	8.2 uF [C1206C825K9RACT U]	80L188EB16 80SCLQ030	82 nF [C0603C823K8RACT U]
8.2 nF [C1210C822K5GACT U]	8.2 uF [C1210C825K3PACT U]	80SCLQ060 80SQ045NG	82 nF [C0805C823K1RACT U]
8.2 nF [C1210C822K5RACT U]	8.2 uF [C1210C825K4PACT U]	80SQ045NRLG 82 mF [C0603C829K2GACT U]	82 nF [C0805C823K3RACT U]
8.2 nF [C1210C822KARACT U]	80C186EA13 80C186EA20	82 mF [C0805C829K5GACT U]	82 nF [C0805C823K4RACT U]
8.2 nF [C1812C822K5GACT U]	80C186EA25 80C186EB13	82 mF [C0805C829KBGAC TU]	82 nF [C0805C823K5RACT U]
8.2 nF [C1812C822K5RACT U]	80C186EB20 80C186EB25	82 nF [C0402C823K4RACT U]	82 nF [C0805C823K8RACT U]
8.2 nF [C1812C822K5RACT U]	80C188EA13 80C188EA20	82 nF [C0402C823K8RACT U]	82 nF [C0805C823M5UAC TU]
8.2 nF [C2220C822K2GACT U]	80C188EA25 80C188EB13	82 nF [C0402C823K9RACT U]	82 nF [C0805F823K3RACT U]
8.2 uF [A700V825M016AT E045]	80C188EB20 80C188EB25	82 nF [C0603C823K3RACT U]	82 nF [C0805F823K4RACT U]
8.2 uF [C1206C825K4PACT U]	80CLQ150 80L186EA13	82 nF [C0603C823K4RACT U]	82 nF [C0805F823K5RACT U]
8.2 uF [C1206C825K8PACT U]	80L186EB13 80L186EB16	82 nF [C0603C823K5RACT U]	82 nF [C1206C823K1RACT U]
8.2 uF [C1206C825K8RACT U]	80L188EA13 80L188EB13		

Multisim 14.0 Power Pro Components

82 nF [C1206C823K2RACT U]	82 nF [C1210C823K1GACT U]	82 nF [C1812C823K1HACT U]	82 pF [C0805C820K1GACT U]
82 nF [C1206C823K3HACT U]	82 nF [C1210C823K1HACT U]	82 nF [C1812C823K5GACT U]	82 pF [C0805C820K2GACT U]
82 nF [C1206C823K3RACT U]	82 nF [C1210C823K1RACT U]	82 nF [C1812C823K5HACT U]	82 pF [C0805C820K3GACT U]
82 nF [C1206C823K5HACT U]	82 nF [C1210C823K3HACT U]	82 nF [C1812C823K5RACT U]	82 pF [C0805C820K5GACT U]
82 nF [C1206C823K5RACT U]	82 nF [C1210C823K5GACT U]	82 nF [C2220C823K1GACT U]	82 pF [C0805C820KBGAC TU]
82 nF [C1206C823KARACT U]	82 nF [C1210C823K5HACT U]	82 nF [C2220C823K2GACT U]	82 pF [C1206C820K1GACT U]
82 nF [C1206C823M5UAC TU]	82 nF [C1210C823K5RACT U]	82 nF [C2220C823K5GACT U]	82 pF [C1206C820K2GACT U]
82 nF [C1206F823K1RACT U]	82 nF [C1210C823KARACT U]	82 pF [C0201C820K3GACT U]	82 pF [C1206C820K5GACT U]
82 nF [C1206F823K3RACT U]	82 nF [C1210C823M1UAC TU]	82 pF [C0402C820K3GACT U]	82 pF [C1206C820KBGAC TU]
82 nF [C1206F823K4RACT U]	82 nF [C1210F823K2RACT U]	82 pF [C0402C820K5GACT U]	82 pF [C1206C820KCGAC TU]
82 nF [C1206F823K5RACT U]	82 nF [C1812C823K1GACT U]	82 pF [C0603C820K5GACT U]	82 pF [C1210C820KBGAC TU]

Multisim 14.0 Power Pro Components

82 pF [C1812C820KBGAC TU]	82 uF [A700V826M006AT E028]	820 nF [C1206F824K4RACT U]	820 nF [C2220C824K1RACT U]
82 pF [C1825C820KBGAC TU]	82 uF [A700V826M2R5AT E018]	820 nF [C1210C824K5RACT U]	820 nF [C2220C824K5RACT U]
82 pF [C2220C820KBGAC TU]	82 uF [A700V826M2R5AT E025]	820 nF [C1210C824K8RACT U]	820 nF [C2220C824KARACT U]
82 pF [C2225C820KBGAC TU]	82 uF [A700V826M2R5AT E028]	820 nF [C1210F824K3RACT U]	820 nF [C2225C824K5RACT U]
82 pF [CA064C820K2GAC TU]	82 uF [T520C826M008AT E025]	820 nF [C1210F824K4RACT U]	820 nF [C2225C824KARACT U]
82 pF [CDR31BP820BKSM]	82 uF [T520C826M008AT E045]	820 nF [C1812C824K5RACT U]	820 pF [C0402C821K1HACT U]
82 uF [A700V826M004AT E018]	820 nF [C0603C824K8PACT U]	820 nF [C1812C824M5UAC TU]	820 pF [C0402C821K3GACT U]
82 uF [A700V826M004AT E025]	820 nF [C0805C824K4RACT U]	820 nF [C1812F824K1RACT U]	820 pF [C0402C821K3HACT U]
82 uF [A700V826M004AT E028]	820 nF [C0805C824K8RACT U]	820 nF [C1812F824K3RACT U]	820 pF [C0402C821K3RACT U]
82 uF [A700V826M006AT E018]	820 nF [C1206C824K3RACT U]	820 nF [C1812F824K5RACT U]	820 pF [C0402C821K4RACT U]
82 uF [A700V826M006AT E025]	820 nF [C1206C824K4RACT U]	820 nF [C1825C824KARACT U]	820 pF [C0402C821K5HACT U]

Multisim 14.0 Power Pro Components

820 pF [C0402C821K5RACT U]	820 pF [C0603C821K5RACT U]	820 pF [C1812C821K2GACT U]	9.1 nF [C0603C912K3HACT U]
820 pF [C0402C821K8RACT U]	820 pF [C0805C821K1RACT U]	820 pF [C1812C821K5GACT U]	9.1 nF [C0805C912K1GACT U]
820 pF [C0603C821K1HACT U]	820 pF [C0805C821K2RACT U]	820 pF [C1812C821KBGAC TU]	9.1 nF [C0805C912K1HACT U]
820 pF [C0603C821K1RACT U]	820 pF [C0805C821K4GACT U]	820 pF [C1825C821KBGAC TU]	9.1 nF [C0805C912K3HACT U]
820 pF [C0603C821K2RACT U]	820 pF [C0805C821K4RACT U]	820 pF [C2220C821KBGAC TU]	9.1 nF [C0805C912K5GACT U]
820 pF [C0603C821K3GACT U]	820 pF [C0805C821K5GACT U]	820 pF [C2225C821KBGAC TU]	9.1 nF [C0805C912K5HACT U]
820 pF [C0603C821K3HACT U]	820 pF [C0805C821K5RACT U]	820 pF [CDR32BP821BKSM]	9.1 nF [C1206C912K1HACT U]
820 pF [C0603C821K3RACT U]	820 pF [C1206C821K1GACT U]	8550-4500PL 87520-0010BLF	9.1 nF [C1206C912K3GACT U]
820 pF [C0603C821K4RACT U]	820 pF [C1206C821K2GACT U]	8EQ045 8EWS08S 8EWS10S	9.1 nF [C1206C912K3HACT U]
820 pF [C0603C821K5GACT U]	820 pF [C1206C821K5GACT U]	8EWS12S 8Line_Bussed	9.1 nF [C1206C912K5HACT U]
820 pF [C0603C821K5HACT U]	820 pF [C1210C821KBGAC TU]	8Line_Isolated 8POS_ROTARY	9.1 nF [CDR35BP912BKSM]
			90CLQ100

Multisim 14.0 Power Pro Components

91 mF [C0805C919KBGAC TU]	910 pF [C0402C911K3HACT U]	910 pF [C2225C911KBGAC TU]	ACB1608L-060
			ACB1608L-120
91 pF [C0805C910K2GACT U]	910 pF [C0402C911K5HACT U]	9Line_Bussed	ACB1608L-300
		9Line_Isolated	ACB1608M-040
91 pF [C0805C910KBGAC TU]	910 pF [C0603C911K1HACT U]	ABC_TO_DQ	ACB1608M-080
		ABM_CURRENT	ACB1608M-120
91 pF [C1206C910K1GACT U]	910 pF [C0603C911K3HACT U]	ABM_VOLTAGE	ACB1608M-300
		AC_CURRENT	ACB1608M-600
91 pF [C1206C910KBGAC TU]	910 pF [C0603C911K5GACT U]	AC_POWER	ACB2012H-015
		ACA3216H4-060	ACB2012H-030
91 pF [C1210C910KBGAC TU]	910 pF [C0603C911K5HACT U]	ACA3216H4-120	ACB2012H-060
		ACA3216H4-300	ACB2012H-120
91 pF [C1812C910KBGAC TU]	910 pF [C0805C911K5GACT U]	ACA3216M3-600	ACB2012H-300
		ACA3216M4-060	ACB2012L-015
91 pF [C1825C910KBGAC TU]	910 pF [C1210C911KBGAC TU]	ACA3216M4-120	ACB2012L-030
		ACA3216M4-300	ACB2012L-060
91 pF [C2220C910KBGAC TU]	910 pF [C1812C911KBGAC TU]	ACA3216M4-600	ACB2012L-120
		ACB1608H-015	ACB2012L-300
91 pF [C2225C910KBGAC TU]	910 pF [C1825C911KBGAC TU]	ACB1608H-030	ACB2012L-600
		ACB1608H-060	ACB2012M-040
910 pF [C0402C911K1HACT U]	910 pF [C2220C911KBGAC TU]	ACB1608H-120	ACB2012M-080
		ACB1608H-300	ACB2012M-120
		ACB1608L-015	ACB2012M-300
		ACB1608L-030	ACB2012M-600
			ACC2012L-250

Multisim 14.0 Power Pro Components

ACC3216L-500	ACPL-214-56AE	ACPL-C79A-000E	ACPL-M50L-000E
ACC4516L-700	ACPL-217-500E	ACPL-C79B-000E	ACPL-M50L-060E
ACF2101BP	ACPL-217-50AE	ACPL-C87AT-000E	ACPL-M61L-000E
ACF2101BU	ACPL-217-50BE	ACPL-H342-000E	ACPL-M61L-060E
ACML-7400-000E	ACPL-217-50CE	ACPL-H342-060E	ACPL-M61T-000E
ACML-7410-000E	ACPL-217-50DE	ACPL-K342-000E	ACPL-M61T-060E
ACML-7420-000E	ACPL-217-560E	ACPL-K342-060E	ACPL-M71T-000E
ACNW261L-000E	ACPL-217-56AE	ACPL-K34T-000E	ACPL-M71T-060E
ACNW261L-300E	ACPL-217-56BE	ACPL-K34T-060E	ACPL-M72T-000E
ACPL-021L-000E	ACPL-217-56CE	ACPL-K43T-000E	ACPL-M72T-060E
ACPL-021L-060E	ACPL-217-56DE	ACPL-K43T-060E	ACPL-P340-000E
ACPL-024L-000E	ACPL-312U-000E	ACPL-K44T-000E	ACPL-P340-060E
ACPL-024L-060E	ACPL-312U-300E	ACPL-K44T-060E	ACPL-P341-000E
ACPL-054L-000E	ACPL-32JT-000E	ACPL-K54L-000E	ACPL-P341-060E
ACPL-054L-060E	ACPL-331J-000E	ACPL-K54L-060E	ACPL-P343-000E
ACPL-061L-000E	ACPL-332J-000E	ACPL-K64L-000E	ACPL-P343-060E
ACPL-061L-060E	ACPL-336J-000E	ACPL-K64L-060E	ACPL-P345-000E
ACPL-064L-000E	ACPL-337J-000E	ACPL-M21L-000E	ACPL-P345-060E
ACPL-064L-060E	ACPL-339J-000E	ACPL-M21L-060E	ACPL-P346-000E
ACPL-077L-000E	ACPL-34JT-000E	ACPL-M43T-000E	ACPL-P346-060E
ACPL-077L-060E	ACPL-782T-000E	ACPL-M43T-060E	ACPL-W340-000E
ACPL-0820-000E	ACPL-782T-300E	ACPL-M46T-000E	ACPL-W340-060E
ACPL-214-500E	ACPL-C61L-000E	ACPL-M46T-060E	ACPL-W341-000E
ACPL-214-50AE	ACPL-C61L-060E	ACPL-M49T-000E	ACPL-W341-060E
ACPL-214-560E	ACPL-C790-000E	ACPL-M49T-060E	ACPL-W343-000E

Multisim 14.0 Power Pro Components

ACPL-W343-060E	AD380KH	AD542KH	AD548JN
ACPL-W345-000E	AD380LH	AD542LH	AD548JR
ACPL-W345-060E	AD380SH	AD542SH	AD548KN
ACPL-W346-000E	AD507JH	AD544JH	AD548SH
ACPL-W346-060E	AD507KH	AD544KH	AD548SQ
ACPL-W50L-000E	AD507SH	AD544LH	AD548TH
ACPL-W50L-060E	AD509JH	AD544SH	AD548TQ
ACPL-W61L-000E	AD509KH	AD545AJH	AD549JH
ACPL-W61L-060E	AD509SH	AD545AKH	AD549KH
ACSL-6400-00TE	AD515AJH	AD545ALH	AD549LH
ACSL-6400-06TE	AD515AKH	AD545AMH	AD549SH
ACSL-7210-00RE	AD515ALH	AD546JN	AD549SH/883B
ACSL-7210-06RE	AD517JH	AD546KN	AD5530_SO16
ACTEL-FLASHPRO-HDR	AD517KH	AD547JH	AD5531_SO16
	AD517LH	AD547KH	AD5539JN
AD1580ART	AD517SH	AD547LH	AD5539JQ
AD1580ARTZ	AD5260_SO14	AD547SH	AD5539SQ
AD1580BKSZ	AD5262_SO16	AD548AH	AD5539SQ/883B
AD1580BRT	AD5280_SO14	AD548AQ	AD581JH
AD1580BRTZ	AD5282_SO16	AD548AR	AD581KH
AD22050N	AD536AJD	AD548BH	AD581LH
AD22050R	AD536AJH	AD548BQ	AD581SH
AD22057N	AD536AJQ	AD548BR	AD581TH
AD22057R	AD536ASE/883B	AD548CH	AD581UH
AD380JH	AD542JH	AD548CQ	AD584JH

Multisim 14.0 Power Pro Components

AD584JN	AD600AQ	AD624CD	AD633JR
AD584KH	AD600AR	AD624SD	AD636JD
AD584KN	AD600JN	AD626AN	AD636JH
AD584LH	AD602AQ	AD626AR	AD636KD
AD584SH	AD602AR	AD626BN	AD636KH
AD584TH	AD602JN	AD627AN	AD637AQ
AD587JN	AD603AQ	AD627AR	AD637AR
AD587JNZ	AD603AR	AD627BN	AD637ARZ
AD587JQ	AD604AN	AD627BR	AD637BR
AD587JR	AD604AR	AD628ARMZ	AD637BRZ
AD587JRZ	AD604ARS	AD628ARZ	AD637JD
AD587KN	AD605AN	AD629AN	AD637JDZ
AD587KR	AD605AR	AD629AR	AD637JQ
AD587KRZ	AD620AN	AD629BN	AD637JRZ
AD587UQ	AD620AR	AD629BR	AD637JRZ-R7
AD588AD	AD620BN	AD630AD	AD637JRZ-RL
AD588AQ	AD620BR	AD630AR	AD637KDZ
AD588ARWZ	AD620SQ	AD630BD	AD637KQ
AD588BD	AD623AN	AD630JN	AD637KRZ
AD588BQ	AD623AR	AD630KN	AD637SD
AD588JQ	AD623ARM	AD630SD	AD637SD/883B
AD588KQ	AD623BN	AD630SE/883B	AD637SQ/883B
AD588SD	AD623BR	AD633AN	AD642JH
AD588TD	AD624AD	AD633AR	AD642KH
AD588TQ/883B	AD624BD	AD633JN	AD642LH

Multisim 14.0 Power Pro Components

AD642SH	AD680JTZ	AD707AQ	AD711SH
AD644JH	AD704AN	AD707AR	AD711SQ
AD644KH	AD704AQ	AD707JN	AD711TH
AD644LH	AD704AR	AD707KN	AD711TQ
AD644SH	AD704BQ	AD707KR	AD712AH
AD645AH	AD704JN	AD707TH	AD712AQ
AD645BH	AD704JR	AD707TQ	AD712BH
AD645JN	AD704JR-16	AD708AH	AD712BQ
AD645KN	AD704KN	AD708AQ	AD712CH
AD645SH	AD704TQ	AD708BH	AD712CQ
AD647JH	AD704TQ/883B	AD708BQ	AD712JN
AD647KH	AD705AQ	AD708JN	AD712JR
AD647LH	AD705BQ	AD708SH	AD712KN
AD647SE	AD705JN	AD708SH/883B	AD712KR
AD647SEB	AD705JR	AD708SQ	AD712SH
AD647SH	AD705KN	AD711AH	AD712SQ
AD648AH	AD705TQ	AD711AQ	AD712SQ/883B
AD648AQ	AD706AQ	AD711BH	AD712TH
AD648BH	AD706AR	AD711BQ	AD712TQ
AD648BQ	AD706BQ	AD711CH	AD712TRZ-EP
AD648CH	AD706JN	AD711CQ	AD713AQ
AD648CQ	AD706JR	AD711JN	AD713BQ
AD680AN	AD706KN	AD711JR	AD713JN
AD680AR	AD706TQ	AD711KN	AD713JR
AD680JR	AD707AH	AD711KR	AD713JR-16

Multisim 14.0 Power Pro Components

AD713KN	AD741LN	AD744TH/883B	AD780BR
AD713SQ	AD741SH	AD744TQ	AD795BH
AD713SQ/883B	AD743AN	AD745AN	AD795JN
AD713TQ	AD743AQ	AD745AQ	AD795JR
AD713TQ/883B	AD743AR	AD745AR	AD795JRZ
AD734AN	AD743BQ	AD745BQ	AD795KN
AD734AQ	AD743JN	AD745JN	AD796AN
AD734BN	AD743JR	AD745JR	AD796AR
AD734BQ	AD743KN	AD745KN	AD796BN
AD734SQ	AD743KR	AD745SQ	AD796SQ/883B
AD734SQ/883B	AD743SQ	AD745SQ/883B	AD797AN
AD736AQ	AD743SQ/883B	AD746AQ	AD797AR
AD736AR	AD744AH	AD746BQ	AD797BN
AD736JNZ	AD744AQ	AD746JN	AD797SQ
AD737AN	AD744BH	AD746JR	AD8000YCPZ
AD737AR	AD744BQ	AD746SQ	AD8000YCPZ-REEL
AD737BQ	AD744CH	AD7510DIJD	AD8000YRDZ
AD741CH	AD744CQ	AD7510DIJN	AD8001AN
AD741CN	AD744JN	AD7510DIJQ	AD8001AQ
AD741H	AD744JR	AD7511DIJD	AD8001AR
AD741JH	AD744KN	AD7511DIJN	AD8001ART
AD741JN	AD744KR	AD7511DIJQ	AD8002AN
AD741KH	AD744SH	AD780AN	AD8002AR
AD741KN	AD744SQ	AD780AR	AD8002ARM
AD741LH	AD744TH	AD780BN	AD8003ACPZ

Multisim 14.0 Power Pro Components

AD8003ACPZ-R2	AD8016ARB	AD8027ARZ-REEL7	AD8032BR
AD8004AN	AD8016ARE	AD8028ARMZ	AD8032BRZ
AD8004AR	AD8016AREZ	AD8028ARZ	AD8033AKS
AD8004AR-14	AD8016ARP	AD8029AKS	AD8033AR
AD8004SQ	AD8017AR	AD8029AR	AD8034AR
AD8005AN	AD8018AR	AD8030AR	AD8034ART
AD8005AR	AD8018ARU	AD8030ARJ	AD8036AN
AD8005ART	AD8021AR	AD8031AN	AD8036AR
AD8007AKS	AD8021ARM	AD8031ANZ	AD8038AKS
AD8007AR	AD8021ARMZ	AD8031AR	AD8038AR
AD8008AR	AD8021ARZ	AD8031ART	AD8039AR
AD8008ARM	AD8022AR	AD8031ARTZ	AD8039ART
AD8009AR	AD8022ARM	AD8031ARZ	AD8040AR
AD8009ARZ	AD8022ARMZ	AD8031BN	AD8040ARU
AD8009JRT	AD8022ARZ	AD8031BNZ	AD8041AN
AD8010AN	AD8023AR	AD8031BR	AD8041AR
AD8010AR	AD8024AR	AD8031BRZ	AD8042AN
AD8010AR-16	AD8027AR	AD8032AN	AD8042AR
AD8011AN	AD8027ART	AD8032ANZ	AD8044AN
AD8011AR	AD8027ARTZ	AD8032AR	AD8044AR
AD8012AR	AD8027ARTZ-R2	AD8032ARM	AD8045ACP
AD8012ARM	AD8027ARTZ-REEL	AD8032ARMZ	AD8045ACPZ-R2
AD8012ARMZ	AD8027ARTZ-REEL7	AD8032ARZ	AD8045ARD
AD8014AR	AD8027ARZ	AD8032BN	AD8045ARDZ
AD8014ART	AD8027ARZ-REEL	AD8032BNZ	AD8047AN

Multisim 14.0 Power Pro Components

AD8047AR	AD8062ARZ	AD810SN	AD8132ARMZ
AD8048AN	AD8065AR	AD810SR	AD8132ARZ
AD8048AR	AD8065ART	AD811AN	AD8133ACP-R2
AD8051AR	AD8065ARTZ	AD811AR-16	AD8137YCP
AD8051ART	AD8065ARZ	AD811AR-20	AD8137YCPZ
AD8052AR	AD8066AR	AD811JR	AD8137YR
AD8052ARM	AD8066ARM	AD811SE/883B	AD8137YRZ
AD8054AR	AD8066ARMZ	AD811SQ/883B	AD8138AR
AD8054ARU	AD8066ARZ	AD8129ARMZ	AD8138ARM
AD8055AN	AD8067ART	AD8129ARMZ-REEL	AD8138ARMZ
AD8055AR	AD8072ARM	AD8129ARMZ-REEL7	AD8138ARZ
AD8055ART	AD8072JN	AD8129ARZ	AD8139ACP
AD8055ARZ	AD8072JR	AD8129ARZ-REEL	AD8139ACPZ
AD8056AN	AD8079AR	AD8129ARZ-REEL7	AD8139ACPZ-R2
AD8056AR	AD8079BR	AD812AN	AD8139ARD
AD8056ARM	AD8091AR	AD812AR	AD8139ARDZ
AD8057AR	AD8091ART	AD8130AR	AD813AN
AD8057ART	AD8092AR	AD8130ARM	AD813AR
AD8058AR	AD8092ARM	AD8131AR	AD813AR-14
AD8058ARM	AD8099ACP	AD8131ARM	AD8145YCPZ-R2
AD8061AR	AD8099ACPZ-R2	AD8131ARMZ	AD8146ACPZ-R2
AD8061ART	AD8099ARD	AD8131ARZ	AD8147ACPZ-R2
AD8062AR	AD8099ARDZ	AD8132AR	AD8148ACPZ-R2
AD8062ARM	AD810AN	AD8132ARM	AD815ARB-24
AD8062ARMZ	AD810AR		AD817AN

Multisim 14.0 Power Pro Components

AD817AR	AD820AR	AD8220BRMZ-R7	AD8226ARMZ
AD8184AN	AD820BN	AD8220BRMZ-RL	AD8226ARZ
AD818AN	AD820BR	AD8220WARMZ	AD8226BRMZ
AD818AR	AD8210WYRZ	AD8220WARMZ-R7	AD8226BRZ
AD8205WHRZ	AD8210YRZ	AD8220WARMZ-RL	AD8227ARMZ
AD8205WHRZ-RL	AD8211YRJZ-R2	AD8221AR	AD8227ARZ
AD8205WYRZ	AD8214ARMZ	AD8221ARM	AD8227BRMZ
AD8205WYRZ-R7	AD8216WYRZ	AD8221BR	AD8227BRZ
AD8205WYRZ-RL	AD8216WYRZ-R7	AD8222ACPZ-R7	AD8228ARMZ
AD8205YRZ	AD8216WYRZ-RL	AD8222BCPZ-R7	AD8228ARZ
AD8205YRZ-R7	AD8216YRZ	AD8222HACPZ-R7	AD8228BRMZ
AD8205YRZ-RL	AD8216YRZ-R7	AD8222HBCPZ-R7	AD8228BRZ
AD8206WYRZ	AD8216YRZ-RL	AD8224ACPZ-R7	AD8229HDZ
AD8206WYRZ-R7	AD8217BRMZ	AD8224ACPZ-RL	AD822AN
AD8206WYRZ-RL	AD8217BRMZ-R7	AD8224ACPZ-WP	AD822AR
AD8206YRZ	AD8217BRMZ-RL	AD8224BCPZ-R7	AD822ARM
AD8206YRZ-REEL	AD8218BCPZ-RL	AD8224BCPZ-RL	AD822BN
AD8206YRZ-REEL7	AD8218BRMZ	AD8224BCPZ-WP	AD822BR
AD8207WBRZ	AD8218BRMZ-R7	AD8224HACPZ-R7	AD822SQ
AD8207WBRZ-R7	AD8219BRMZ	AD8224HACPZ-RL	AD8235ACBZ-P7
AD8207WBRZ-RL	AD8219BRMZ-RL	AD8224HACPZ-WP	AD8236ARMZ
AD8208WBRMZ	AD8220ARMZ	AD8224HBCPZ-R7	AD8237ARMZ
AD8208WBRZ	AD8220ARMZ-R7	AD8224HBCPZ-RL	AD8237ARMZ-R7
AD8209WBRMZ	AD8220ARMZ-RL	AD8224HBCPZ-WP	AD8237ARMZ-RL
AD820AN	AD8220BRMZ	AD8225AR	AD823AN

Multisim 14.0 Power Pro Components

AD823AR	AD8274ARZ-RL	AD829JR	AD8332ARUZ-RL
AD8244ARMZ	AD8275ARMZ	AD829SE/883B	AD8333ACPZ-REEL
AD8244BRMZ	AD8275BRMZ	AD829SQ	AD8333ACPZ-REEL7
AD824AN	AD8276ARMZ	AD829SQ/883B	AD8333ACPZ-WP
AD824AR-14	AD8276ARZ	AD8304ARU	AD8334ACPZ
AD824AR-16	AD8276BRMZ	AD830AN	AD8334ACPZ-REEL
AD824BN	AD8276BRZ	AD830JR	AD8334ACPZ-REEL7
AD8250ARMZ	AD8277ARZ	AD8310ARM	AD8335ACPZ
AD8251ARMZ	AD8277BRZ	AD8330ACPZ-R2	AD8335ACPZ-REEL
AD8253ARMZ	AD8278ARMZ	AD8330ACPZ-R7	AD8335ACPZ-REEL7
AD8253ARMZ-R7	AD8278ARZ	AD8330ACPZ-RL	AD8336ACPZ-R7
AD8253ARMZ-RL	AD8278BRMZ	AD8330ARQZ	AD8336ACPZ-RL
AD825AR	AD8278BRZ	AD8330ARQZ-R7	AD8336ACPZ-WP
AD825AR-16	AD8279ARZ	AD8330ARQZ-RL	AD8337BCPZ-R2
AD826AN	AD8279BRZ	AD8331ARQZ	AD8337BCPZ-REEL
AD826AR	AD827AQ	AD8331ARQZ-R7	AD8337BCPZ-REEL7
AD8270ACPZ-R7	AD827JN	AD8331ARQZ-RL	AD8337BCPZ-WP
AD8273ARZ	AD827JR-16	AD8332ACPZ-R2	AD8338ACPZ-R7
AD8273ARZ-R7	AD827SE/883B	AD8332ACPZ-R7	AD8338ACPZ-RL
AD8273ARZ-RL	AD827SQ	AD8332ACPZ-RL	AD8397ARDZ
AD8274ARMZ	AD827SQ/883B	AD8332ARU	AD8397ARZ
AD8274ARMZ-R7	AD828AN	AD8332ARU-REEL	AD840JN
AD8274ARMZ-RL	AD828AR	AD8332ARU-REEL7	AD840JQ
AD8274ARZ	AD829AQ	AD8332ARUZ	AD840KN
AD8274ARZ-R7	AD829JN	AD8332ARUZ-R7	AD840KQ

Multisim 14.0 Power Pro Components

AD840SE-883B	AD8420ARMZ	AD8422BRMZ-R7	AD8436ACPZ-WP
AD840SQ	AD8420ARMZ-R7	AD8422BRMZ-RL	AD8436ARQZ
AD840SQ-883B	AD8420ARMZ-RL	AD8422BRZ	AD8436ARQZ-R7
AD8417BRMZ	AD8421ARMZ	AD8422BRZ-R7	AD8436ARQZ-RL
AD8417WBRMZ	AD8421ARMZ-R7	AD8422BRZ-RL	AD8436BRQZ
AD8417WBRZ	AD8421ARMZ-RL	AD8426ACPZ-R7	AD8436BRQZ-R7
AD8417WHRMZ	AD8421ARZ	AD8426ACPZ-WP	AD8436BRQZ-RL
AD8417WHRZ	AD8421ARZ-R7	AD8426BCPZ-R7	AD8436JCPZ-R7
AD8418ABRMZ	AD8421ARZ-RL	AD8426BCPZ-WP	AD8436JCPZ-RL
AD8418AWBRMZ	AD8421BRMZ	AD8429ARZ	AD8436JCPZ-WP
AD8418AWBRZ	AD8421BRMZ-R7	AD8429ARZ-R7	AD843AQ
AD8418AWHRMZ	AD8421BRMZ-RL	AD8429BRZ	AD843BH
AD8418AWHRZ	AD8421BRZ	AD8429BRZ-R7	AD843BQ
AD8418BRMZ	AD8421BRZ-R7	AD842JH	AD843JN
AD8418WBRMZ	AD8421BRZ-RL	AD842JN	AD843JR
AD8418WBRZ	AD8421TRMZ-EP	AD842JQ	AD843JR-16
AD841JH	AD8421TRMZ-EP-R7	AD842JR	AD843KN
AD841JN	AD8422ARMZ	AD842KH	AD843SE
AD841JQ	AD8422ARMZ-R7	AD842KN	AD843SE/883B
AD841KH	AD8422ARMZ-RL	AD842KQ	AD843SH
AD841KN	AD8422ARZ	AD842SE	AD843SQ
AD841KQ	AD8422ARZ-R7	AD842SH	AD843SQ/883B
AD841SE	AD8422ARZ-RL	AD842SQ	AD844AN
AD841SH	AD8422BRMZ	AD8436ACPZ-R7	AD844AQ
AD841SQ		AD8436ACPZ-RL	AD844BQ

Multisim 14.0 Power Pro Components

AD844JRZ-16	AD8476ACPZ-R7	AD848SQ	AD8504ARUZ
AD844SQ	AD8476ACPZ-RL	AD848SQ/883B	AD8505ACBZ-R7
AD8450ASTZ	AD8476ACPZ-WP	AD8494ARMZ	AD8505ARJZ-RL
AD8451ASTZ	AD8476ARMZ	AD8494ARMZ-R7	AD8506ARMZ
AD845AQ	AD8476ARMZ-R7	AD8494CRMZ	AD8508ACBZ-REEL
AD845BQ	AD8476ARMZ-RL	AD8494CRMZ-R7	AD8508ARUZ
AD845JN	AD8476BCPZ-R7	AD8495ARMZ	AD8510AR
AD845JR	AD8476BCPZ-RL	AD8495ARMZ-R7	AD8510ARM
AD845JR-16	AD8476BCPZ-WP	AD8495CRMZ	AD8510BR
AD845KN	AD8476BRMZ	AD8495CRMZ-R7	AD8512AR
AD845SQ	AD8476BRMZ-R7	AD8496ARMZ	AD8512ARM
AD845SQ/883B	AD8476BRMZ-RL	AD8496ARMZ-R7	AD8512BR
AD846AN	AD8479ARZ	AD8496CRMZ	AD8513AR
AD846AQ	AD8479ARZ-RL	AD8496CRMZ-R7	AD8513ARU
AD846BQ	AD8479BRZ	AD8497ARMZ	AD8515AKS
AD846SQ	AD8479BRZ-RL	AD8497ARMZ-R7	AD8515ART
AD8475ACPZ-R7	AD847AQ	AD8497CRMZ	AD8517ART
AD8475ACPZ-RL	AD847AR	AD8497CRMZ-R7	AD8519AKS
AD8475ACPZ-WP	AD847JN	AD849AQ	AD8519AR
AD8475ARMZ	AD847JR	AD849JN	AD8519ART
AD8475ARMZ-R7	AD847SQ	AD849JR	AD8527AR
AD8475ARMZ-RL	AD847SQ/883B	AD849SQ	AD8529AR
AD8475BRMZ	AD848AQ	AD849SQ/883B	AD8529ARM
AD8475BRMZ-R7	AD848JN	AD8500AKSZ	AD8531AKS
AD8475BRMZ-RL	AD848JR	AD8502ARJZ	AD8531AR

Multisim 14.0 Power Pro Components

AD8532AR	AD8552AR	AD8602AR	AD8612ARU
AD8532ARM	AD8552ARU	AD8602ARM	AD8613AKSZ
AD8532ARU	AD8554AR	AD8603AUJZ	AD8613AUJZ
AD8534AR	AD8554ARU	AD8604AR	AD8614ART
AD8534ARU	AD8561AN	AD8604ARQZ	AD8615AUJZ
AD8538ARZ	AD8561AR	AD8604ARUZ	AD8616AR
AD8538AUJZ	AD8561ARU	AD8604DRU	AD8616ARM
AD8538AUJZ-R2	AD8564AN	AD8604DRZ	AD8617ACPZ-R2
AD8539ARMZ	AD8564AR	AD8605ACB	AD8617ARMZ
AD8539ARZ	AD8565AKS	AD8605ART	AD8617ARZ
AD8541AKS	AD8565AKSZ	AD8606ACBZ-REEL	AD8617WARMZ-REEL
AD8541AR	AD8571AR	AD8606AR	AD8617WARZ-RL
AD8541ART	AD8571ARM	AD8606ARM-REEL	AD8618AR
AD8541ARZ	AD8572AR	AD8607AR	AD8618ARU
AD8542AR	AD8572ARU	AD8607ARM-REEL	AD8619ARUZ
AD8542ARM	AD8574AR	AD8608AR	AD8619ARZ
AD8542ARU	AD8574ARU	AD8608ARU	AD8620AR
AD8544AR	AD8591ART	AD8609AR	AD8620BR
AD8544ARU	AD8592ARM	AD8609ARU	AD8622ARMZ
AD8546ARMZ	AD8594AR	AD8610AR	AD8622ARZ
AD8548ARZ	AD8594ARU	AD8610ARM	AD8624ACPZ-R2
AD8548ARZ-R7	AD8597ACPZ-R2	AD8610ARZ	AD8624ARUZ
AD8548ARZ-RL	AD8597ARZ	AD8610BR	AD8625ARUZ
AD8551AR	AD8599ARZ	AD8611AR	AD8625ARZ
AD8551ARM	AD8601ART	AD8611ARM	

Multisim 14.0 Power Pro Components

AD8626ARMZ	AD8639ARZ	AD8657ARMZ	AD8674ARU
AD8626ARZ	AD8639WARZ	AD8659ACPZ-R7	AD8675ARMZ
AD8627AKS	AD8641AKSZ	AD8659ACPZ-RL	AD8675ARZ
AD8627AKSZ	AD8641AKSZ-R2	AD8659ARZ	AD8676ARMZ
AD8627AR	AD8641ARZ	AD8659ARZ-R7	AD8676ARZ
AD8627ARZ	AD8642ARMZ	AD8659ARZ-RL	AD8676BRMZ
AD8628AR	AD8642ARZ	AD8661ACPZ-R2	AD8676BRZ
AD8628ART	AD8643ACPZ-R2	AD8661ARZ	AD8677ARZ
AD8628AUJ	AD8643ARZ	AD8662ARMZ	AD8677AUJZ-R2
AD8629ARMZ	AD8644AR	AD8662ARZ	AD8691AKSZ
AD8629ARZ	AD8644ARU	AD8663ACPZ	AD8691AUJZ
AD8629WARZ-RL	AD8646ARMZ	AD8663ARZ	AD8692ARMZ
AD8630ARUZ	AD8646ARZ	AD8664ARUZ	AD8692ARZ
AD8630ARZ	AD8646WARMZ-RL	AD8664ARZ	AD8694ARUZ
AD8630WARZ-RL	AD8646WARZ-RL	AD8667ARMZ	AD8694ARZ
AD8631ART	AD8648ARUZ	AD8667ARZ	AD8698AR
AD8631ARTZ	AD8648ARZ	AD8669ARUZ	AD8698ARM
AD8632AR	AD8648WARUZ	AD8669ARZ	AD9218_FP48
AD8632ARM	AD8651AR	AD8671AR	AD9610TH
AD8632ARMZ	AD8651ARM	AD8671ARM	AD9610TH/883B
AD8632ARZ	AD8655ARMZ	AD8671ARMZ	AD9617AQ
AD8638ARJZ	AD8655ARZ	AD8672AR	AD9617BQ
AD8638ARZ	AD8656ARMZ	AD8672ARM	AD9617JN
AD8639ACPZ-R2	AD8656ARZ	AD8672ARMZ	AD9617JR
AD8639ARMZ	AD8657ACPZ-RL	AD8674AR	AD9617SQ

Multisim 14.0 Power Pro Components

AD9617TQ	ADA4000-2ARMZ	ADA4004-4ARZ-RL	ADA4077-2BRZ-RL
AD9618AQ	ADA4000-2ARZ	ADA4051-1AKSZ-R2	ADA4077-4ARUZ
AD9618BQ	ADA4000-4ARUZ	ADA4051-1ARJZ-R2	ADA4077-4ARZ
AD9618JN	ADA4000-4ARZ	ADA4051-2ACPZ-R2	ADA4084-2ARMZ
AD9618JR	ADA4001-2ARZ	ADA4051-2ARMZ	ADA4084-2ARMZ-R7
AD9618SQ	ADA4001-2ARZ-R7	ADA4062-2ACPZ-RL	ADA4084-2ARMZ-RL
AD9618TQ	ADA4001-2ARZ-RL	ADA4062-2ARMZ	
AD9620AD	ADA4004-1ARJZ-R2	ADA4062-2ARZ	ADA4084-2ARZ
AD9620SD	ADA4004-1ARJZ-R7	ADA4062-2BRZ	ADA4084-2ARZ-R7
AD9621AN	ADA4004-1ARJZ-RL	ADA4062-4ACPZ-R2	ADA4084-2ARZ-RL
AD9622AN	ADA4004-1ARZ	ADA4062-4ARUZ	ADA4091-2ACPZ-R2
AD9623AN	ADA4004-1ARZ-R7	ADA4075-2ACPZ-RL	ADA4091-2ARZ
AD9624AN	ADA4004-1ARZ-RL	ADA4075-2ARZ	ADA4091-4ACPZ-R2
AD9630AN	ADA4004-2ARMZ	ADA4077-1ARMZ	ADA4091-4ARUZ
AD9630AQ	ADA4004-2ARMZ-R7	ADA4077-1ARZ	ADA4092-4ARUZ
AD9630AR		ADA4077-1BRZ	ADA4096-2ACPZ-R7
AD9631AN	ADA4004-2ARMZ-RL	ADA4077-2ARMZ	ADA4096-2ARMZ
AD9631AR	ADA4004-2ARZ	ADA4077-2ARMZ-R7	ADA4096-2WARMZ-R7
AD9632AN	ADA4004-2ARZ-R7	ADA4077-2ARMZ-RL	ADA4096-2WARMZ-RL
AD9632AR	ADA4004-2ARZ-RL		
AD9841A-LQFP(48)	ADA4004-4ACPZ-R2	ADA4077-2ARZ	ADA4096-4ACPZ-R7
AD9842A-LQFP(48)	ADA4004-4ACPZ-R7	ADA4077-2ARZ-R7	ADA4096-4ARUZ
ADA4000-1ARZ	ADA4004-4ACPZ-RL	ADA4077-2ARZ-RL	ADA4500-2ACPZ-R7
ADA4000-1AUJZ	ADA4004-4ARZ	ADA4077-2BRZ	ADA4500-2ACPZ-RL
ADA4000-1AUJZ-RL	ADA4004-4ARZ-R7	ADA4077-2BRZ-R7	

Multisim 14.0 Power Pro Components

ADA4500-2ARMZ	ADA4627-1ARZ	ADA4691-2ACBZ-R7	ADA4851-1YRJZ-R2
ADA4500-2ARMZ-R7	ADA4627-1BRZ	ADA4691-2ACPZ-R7	ADA4851-1YRJZ-RL
ADA4500-2ARMZ-RL	ADA4637-1ACPZ-R2	ADA4691-4ACPZ-R7	ADA4851-2WYRMZ
ADA4505-1ACBZ-R7	ADA4637-1ARZ	ADA4692-2ACPZ-R7	ADA4851-2YRMZ
ADA4505-1ARJZ-R2	ADA4637-1BRZ	ADA4692-2ARZ	ADA4851-2YRMZ-RL
ADA4505-2ACBZ-RL	ADA4638-1ACPZ-R7	ADA4692-4ARUZ	ADA4851-4WYRUZ
ADA4505-2ARMZ	ADA4638-1ACPZ-RL	ADA4700-1ARDZ	ADA4851-4YRUZ
ADA4505-4ACBZ-RL	ADA4638-1ARZ	ADA4805-1AKSZ-R2	ADA4851-4YRUZ-RL
ADA4505-4ARUZ	ADA4638-1ARZ-R7	ADA4805-1ARJZ-R2	ADA4853-1AKSZ-R2
ADA4528-1ARMZ	ADA4638-1ARZ-RL	ADA4817-1ACPZ-R2	ADA4853-2YCPZ-R2
ADA4610-2ACPZ-R7	ADA4661-2ACPZ-R7	ADA4817-1ACPZ-R7	ADA4853-3WYCPZ-R7
ADA4610-2ACPZ-RL	ADA4661-2ACPZ-RL	ADA4817-1ACPZ-RL	ADA4853-3YCPZ-R2
ADA4610-2ARMZ	ADA4661-2ARMZ	ADA4817-1ARDZ	ADA4853-3YRUZ
ADA4610-2ARMZ-R7	ADA4661-2ARMZ-R7	ADA4817-1ARDZ-R7	ADA4855-3YCPZ-R2
ADA4610-2ARMZ-RL	ADA4661-2ARMZ-RL	ADA4817-1ARDZ-RL	ADA4857-1YCPZ-R2
ADA4610-2ARZ	ADA4665-2ARMZ	ADA4817-2ACPZ-R7	ADA4857-1YRZ
ADA4610-2ARZ-R7	ADA4665-2ARZ	ADA4817-2ACPZ-RL	ADA4857-2YCPZ-R2
ADA4610-2ARZ-RL	ADA4666-2ACPZ-R7	ADA4841-1YRZ	ADA4858-3ACPZ-R2
ADA4610-2BRZ	ADA4666-2ACPZ-RL	ADA4850-1YCPZ	ADA4860-1YRJZ-R2
ADA4610-2BRZ-R7	ADA4666-2ARMZ	ADA4850-1YCPZ-R2	ADA4860-1YRJZ-RL
ADA4610-2BRZ-RL	ADA4666-2ARMZ-R7	ADA4850-2YCPZ-R2	ADA4860-1YRJZ-RL7
ADA4627-1ACPZ-RL	ADA4666-2ARMZ-RL	ADA4850-2YCPZ-RL	ADA4861-3YRZ
		ADA4851-1WYRJZ-R7	ADA4861-3YRZ-RL

Multisim 14.0 Power Pro Components

ADA4861-3YRZ-RL7	ADA4897-2ARMZ	ADA4940-2ACPZ-R2	ADG1311YRZ
ADA4870ARRZ	ADA4897-2TRMZ-EP	ADA4940-2ACPZ-R7	ADG1312YRUZ
ADA4891-1ARJZ-R7	ADA4898-1YRDZ	ADA4940-2ACPZ-RL	ADG1312YRZ
ADA4891-1ARZ	ADA4898-2YRDZ	ADA4941-1YCPZ-RL	ADG1313YRUZ
ADA4891-2ARMZ	ADA4899-1YCPZ	ADA4941-1YRZ	ADG1313YRZ
ADA4891-2ARZ	ADA4899-1YCPZ-R2	ADA4950-1YCPZ-R2	ADG201ABQ
ADA4891-3ARUZ	ADA4899-1YRDZ	ADA4950-2YCPZ-R2	ADG201AKN
ADA4891-3ARZ	ADA4922-1ACPZ-R2	ADA4960-1ACPZ-R2	ADG201AKP
ADA4891-4ARUZ	ADA4922-1ARDZ	ADC	ADG201AKR
ADA4891-4ARZ	ADA4927-1YCPZ-R2	ADC16	ADG201ATE
ADA4895-2ARMZ	ADA4927-2YCPZ	ADD_FULL	ADG201ATQ
ADA4895-2ARMZ-R7	ADA4930-1YCPZ-R2	ADD_FULL4_FCR	ADG201HSTE
ADA4895-2ARMZ-RL	ADA4930-2YCPZ-R2	ADD_HALF	ADG406BN
ADA4896-2ACPZ-R2	ADA4932-1YCPZ-R2	ADG1211YCPZ-500RL7	ADG406BP
ADA4896-2ACPZ-R7	ADA4932-2YCPZ-R2	ADG1211YRUZ	ADG407BN
ADA4896-2ACPZ-RL	ADA4937-1YCPZ-R2	ADG1212YCPZ-500RL7	ADG407BP
ADA4896-2ARMZ	ADA4937-2YCPZ-R2	ADG1212YRUZ	ADG408
ADA4896-2ARMZ-R7	ADA4938-1ACPZ-R2	ADG1213YCPZ-500RL7	ADG408BN
ADA4896-2ARMZ-RL	ADA4938-2ACPZ-R2	ADG1213YRUZ	ADG408BR
ADA4897-1ARJZ-R2	ADA4939-1YCPZ-R2	ADG1236YCPZ-500RL7	ADG408BRU
ADA4897-1ARZ	ADA4940-1ACPZ-R2	ADG1236YRUZ	ADG408TQ
ADA4897-1SRJZ-EPR7	ADA4940-1ACPZ-RL	ADG1311YRUZ	ADG409BN
			ADG409BR
			ADG409BRU
			ADG409TQ

Multisim 14.0 Power Pro Components

ADG411	ADG441BN	ADG511BR	ADG609BN
ADG411BN	ADG441BR	ADG511PM5	ADG609BR
ADG411BR	ADG441TQ	ADG511TQ	ADG609BRU
ADG411BRU	ADG442BN	ADG512BN	ADG609BRUZ
ADG411BRUZ	ADG442BR	ADG512BR	ADG609BRZ
ADG411BRZ	ADG442SQ	ADG512PM5	ADG611YRUZ
ADG411TQ	ADG444	ADG512TQ	ADG611YRZ
ADG412	ADG444ABN	ADG513BN	ADG612WYRUZ-REEL
ADG412BN	ADG444ABR	ADG513BR	ADG612YRUZ
ADG412BR	ADG444BN	ADG513PM5	ADG613YRUZ
ADG412BRU	ADG444BR	ADG513TQ	ADG658YCPZ
ADG412BRUZ	ADG444S	ADG528F	ADG658YRQ
ADG412BRZ	ADG508FBN	ADG528FBN	ADG658YRU
ADG412TQ	ADG508FBNZ	ADG528FBP	ADG659YCPZ
ADG413BN	ADG508FBRN	ADG528FTQ	ADG659YRQ
ADG413BNZ	ADG508FBRUZ	ADG601BRMZ	ADG659YRU
ADG413BR	ADG508FBRW	ADG601BRTZ-REEL	ADG663BRU
ADG413BRUZ	ADG508FTQ	ADG602BRM	ADG701BRJ-500RL7
ADG413BRZ	ADG509FBN	ADG602BRTZ-REEL	ADG701BRM
ADG426BN	ADG509FBRN	ADG604YRU	ADG701BRTZ-REEL
ADG426BRS	ADG509FBRUZ	ADG604YRUZ	ADG702BRJ-REEL7
ADG431BR	ADG509FBRW	ADG608BN	ADG702BRM
ADG432BR	ADG509FBRWZ	ADG608BR	ADG702BRTZ-REEL
ADG441ABN	ADG509FTQ	ADG608BRU	ADG711BR
ADG441ABR	ADG511BN	ADG608TRU	

Multisim 14.0 Power Pro Components

ADG711BRU	ADG801BRM	ADG859BRYZ-REEL	ADSP-2105-PLCC(68)
ADG712BR	ADG801BRT-500RL7	ADG859YRYZ-REEL	ADSP-2111-PGA(100)
ADG712BRU	ADG802BCBZ-REEL7	ADG884BCBZ-REEL	ADSP-2111-PQFP(100)
ADG713BR	ADG802BRM	ADG884BCPZ-REEL	ADSP-2115-PLCC(68)
ADG713BRU	ADG802BRT-500RL7	ADG884BRMZ	ADSP-2115-PQFP(80)
ADG719BRM	ADG811YCPZ-REEL	ADR3425ARJZ-R2	ADSP-2115-TQFP(80)
ADG719BRT-REEL	ADG811YRU	ADR3425ARJZ-R7	ADSP-2161-PLCC(68)
ADG721ACPZ-REEL	ADG812YRU	ADR5040AKSZ-R2	ADSP-2161-PQFP(80)
ADG721BRM	ADG813YRU	ADR5040ARTZ-R2	ADSP-2162-PLCC(68)
ADG722ACPZ-REEL	ADG819BCB	ADR5040BKSZ-R2	ADSP-2162-PQFP(80)
ADG722BRM	ADG819BRM	ADR5040BRTZ-R2	ADSP-2163-PQFP(80)
ADG723ACPZ-REEL	ADG819BRT	ADS8320EB	ADSP-2163-PLCC(68)
ADG723BRM	ADG820BRM	ADS8322YB	ADSP-2163-TQFP(80)
ADG741BKSZ5-REEL	ADG821BRM	ADS8364Y	ADSP-2101-PGA(68)
ADG741BKSZ-REEL	ADG822BRM	ADSP-2101-PLCC(68)	ADSP-2101-PLCC(68)
ADG742BKSZ5-REEL	ADG823BRM	ADSP-2101-PQFP(80)	ADSP-2101-PQFP(80)
ADG742BKSZ-R2	ADG839YKSZ-500RL7	ADSP-2101-TQFP(80)	ADSP-2103-PLCC(68)
ADG749BKSZ-REEL	ADG841YKSZ-500RL7	ADSP-2103-PQFP(80)	ADSP-2103-PQFP(80)
ADG779BKSZ-R2	ADG842YKSZ-500RL7	ADSP-2103-TQFP(80)	ADSP-2103-TQFP(80)
ADG781BCP	ADG849YKSZ-500RL7		
ADG782BCP			
ADG783BCP			
ADG787BCBZ-REEL			
ADG787BCPZ-REEL			
ADG787BRMZ			

Multisim 14.0 Power Pro Components

ADSP-2164-PLCC(68)	ALPHA_NUMERIC_COM_A_YELLOW	AM29521APC	ANALOG_INV
ADSP-2164-PQFP(80)	ALPHA_NUMERIC_COM_K_BLUE	AM29521APCB	ANALOG_OR
ADSP-2164-TQFP(80)	ALPHA_NUMERIC_COM_K_GREEN	AM29705DC	ANALOG_SR_LATCH
ADSP-2191M-LQFP(144)	ALPHA_NUMERIC_COM_K_ORANGE	AM29705PC	ANALOG_SWITCH_VIRTUAL
ADTL082ARMZ	ALPHA_NUMERIC_COM_K_RED	AM29LV800BB-70EI	AND_OR_I
ADTL082ARZ	ALPHA_NUMERIC_COM_K_YELLOW	AMMETER_H	AND2
ADTL082JR	ALTERA-BYTEBLASTER-HDR	AMMETER_HR	AND2
ADTL082JRZ	ALU_4BIT	AMMETER_V	AND3
ADTL084ARUZ	AM_VOLTAGE	AMMETER_VR	AND3
ADTL084ARZ	AM26LS31CD	AMP01AX	AND4
ADTL084JR	AM26LS32AC	AMP01BX	AND4
ADTL084JRZ	AM29520ADC	AMP01EX	AND4
ADZS-BRKOUT-EX3	AM29520ADCB	AMP01FX	AND5
AIR_NC	AM29520AJC	AMP01GS	AND5
AIR_NO	AM29520ALC	AMP02AZ	AND6
ALPHA_NUMERIC_COM_A_BLUE	AM29520APC	AMP02EP	AND6
ALPHA_NUMERIC_COM_A_GREEN	AM29520APCB	AMP02ES	AND7
ALPHA_NUMERIC_COM_A_ORANGE	AM29521ADC	AMP02FP	AND7
ALPHA_NUMERIC_COM_A_RED	AM29521ADCB	AMP02FS	AND8
	AM29521AJC	AMP04EP	AND8
	AM29521ALC	AMP04ES	ANGLE_WRAP
		AMP04FP	ANTI_PLUG
		AMP04FS	ARBITRARY_LAPLACE_FUNCTION
		AMPSIMP	ARBITRARY_LOAD
		ANALOG_AND	

Multisim 14.0 Power Pro Components

ARBITRARY_LOGIC_BLOCK_16_16	ATP405-TL-H	AUIRFS8408TRR	BA158GP
ARBITRARY_LOGIC_BLOCK_4_4	ATV2500BL-20JI	AUIRFS8408	BA159-E3/54
ARBITRARY_LOGIC_BLOCK_8_8	ATV2500BQ-20JC	AUIRFS8408	BA159GP
ARBITRARY_SPICE_BLOCK	AUIRF2903ZL	AUIRFU4292	BA220
ARM-14-HDR	AUIRF2903ZS	AUIRFZ44VZS	BA221
ARM-20-HDR	AUIRF3004WL	AUIRGDC0250	BA223
ASP-134488-01	AUIRF7303QTR	AUIRGP4063D	BA281
ASP-134603-01	AUIRF7640S2TR	AUIRGP4063D-E	BA314
ASP-134604-01	AUIRF7647S2TR	AUIRGP4066D1	BA315
ASP-134606-01	AUIRF7648M2TR	AUIRGP4066D1-E	BA316
ASSR-V621-002E	AUIRF7669L2TR	AUIRGP50B60PD1	BA317
ASSR-V621-302E	AUIRF7734M2TR	AUIRGP50B60PD1E	BA318
ASSR-V622-002E	AUIRF7736M2TR	AUIRGPS4067D1	BA423
ASSR-V622-302E	AUIRF7737L2TR	AUIRGR4045D	BA423L
ATF750C-10PC	AUIRF7738L2TR	AUIRGR4045DTR	BA481
ATF750C-10XC	AUIRF7739L2TR	AUIRGR4045DTRL	BA482
ATF750C-15PC	AUIRFR4292	AUIRGR4045DTRR	BA483
ATF750C-15XC	AUIRFR4292TRL	AUIRGU4045D	BA484
ATF750CL-15PC	AUIRFR4292TRR	AUIRLS3034-7P	BA592
ATF750CL-15XC	AUIRFS6535	AUIRLS3034-7TRL	BA595
ATP207-TL-H	AUIRFS6535TRL	AUIRLS3114Z	BA682
ATP301-TL-H	AUIRFS8407	AUIRLS3114ZTRL	BA683
	AUIRFS8407TRL	AVR-JTAG-HDR	BA885
	AUIRFS8408	B6S-E3/80	BA892
	AUIRFS8408TRL	BA157GP	BA895

Multisim 14.0 Power Pro Components

BAL74	BAR16-1	BAR99	BAS16VY
BAL99	BAR50-02L	BAS101	BAS16W
BAR_LED_BLUE	BAR50-02V	BAS101S	BAS17
BAR_LED_BLUE_FOUR	BAR61	BAS11	BAS170W
BAR_LED_BLUE_TEN	BAR63-02L	BAS116	BAS19
BAR_LED_BLUE_TEN	BAR63-02V	BAS116H	BAS20
BAR_LED_GREEN	BAR63-02W	BAS116LT1G	BAS20LT1G
BAR_LED_GREEN_FOUR	BAR63-03W	BAS116T	BAS21
BAR_LED_GREEN_TEN	BAR63-04	BAS116TT1G	BAS21AVD
BAR_LED_ORANGE	BAR63-04W	BAS125-04W	BAS21AW
BAR_LED_ORANGE_FOUR	BAR63-05	BAS125-05W	BAS21H
BAR_LED_ORANGE_TEN	BAR63-05W	BAS125-07W	BAS21HT1G
BAR_LED_ORANGE_TEN	BAR63-06	BAS140W	BAS21J
BAR_LED_RED	BAR63-06W	BAS15	BAS21M3T5G
BAR_LED_RED_FOUR	BAR64-02V	BAS16	BAS21SLT1G
BAR_LED_RED_TEN	BAR64-03W	BAS16-02L	BAS21SW
BAR_LED_RED_FOUR	BAR64-04	BAS16DXV6T1G	BAS21TMR6T1G
BAR_LED_RED_TEN	BAR64-04W	BAS16H	BAS21U
BAR_LED_YELLOW	BAR64-05W	BAS16J	BAS21VD
BAR_LED_YELLOW_FOUR	BAR64-06W	BAS16L	BAS21W
BAR_LED_YELLOW_TEN	BAR65-03W	BAS16LD	BAS28
BAR_LED_YELLOW_TEN	BAR67-02V	BAS16M3T5G	BAS29
BAR14-1	BAR74	BAS16P2T5G	BAS3010B-03W
BAR15-1	BAR81W	BAS16T	BAS3020B
	BAR88-02V	BAS16VV	BAS31

Multisim 14.0 Power Pro Components

BAS316	BAS516	BAS85	BAT18
BAS32	BAS521	BAS86	BAT18-04
BAS321	BAS56	BAT120A	BAT18-05
BAS32L	BAS70	BAT120C	BAT24-02LS
BAS35	BAS70-02L	BAT120S	BAT240A
BAS40	BAS70-02W	BAT14_098	BAT46WH
BAS40-02L	BAS70-04	BAT15_03W	BAT46WJ
BAS40-04	BAS70-04LT1G	BAT15_04	BAT54
BAS40-05	BAS70-04W	BAT15_098	BAT54A
BAS40-05V	BAS70-05	BAT15_099	BAT54AW
BAS40-05W	BAS70-05W	BAT15_099R	BAT54C
BAS40-06	BAS70-06	BAT15-02LRH	BAT54CLT1
BAS40-06W	BAS70-06W	BAT15-03W	BAT54CLT1G
BAS40-07	BAS70-07	BAT15-05W	BAT54CLT3G
BAS40-07V	BAS70-07S	BAT15-099	BAT54CM
BAS40-07W	BAS70-07V	BAT160A	BAT54CV
BAS40H	BAS70H	BAT160C	BAT54CW
BAS40L	BAS70L	BAT160S	BAT54H
BAS40W	BAS70VV	BAT165	BAT54J
BAS40XY	BAS70W	BAT17	BAT54L
BAS416	BAS70XY	BAT17-04	BAT54M3T5G
BAS45	BAS716	BAT17-05	BAT54S
BAS45A	BAS81	BAT17-05W	BAT54SW
BAS45AL	BAS82	BAT17-06W	BAT54T
BAS45L	BAS83	BAT17-07	BAT54VV

Multisim 14.0 Power Pro Components

BAT54W	BAT68-06	BAT960	BAV70M3T5G
BAT54WT1G	BAT68-06W	BAV10	BAV70S
BAT54XY	BAT720	BAV100	BAV70T
BAT60A	BAT721	BAV101	BAV70TT1G
BAT60B	BAT721A	BAV102	BAV70W
BAT62	BAT721C	BAV103	BAV74
BAT62-02L	BAT721S	BAV105	BAV74LT1
BAT62-02W	BAT74	BAV170	BAV74LT1G
BAT62-03W	BAT74S	BAV18	BAV756S
BAT62-07W	BAT74V	BAV19	BAV99
BAT63	BAT754	BAV199	BAV99LT1
BAT63-07W	BAT754A	BAV199W	BAV99LT1G
BAT64	BAT754C	BAV20	BAV99LT3
BAT64-02W	BAT754L	BAV21	BAV99LT3G
BAT64-04	BAT754S	BAV23	BAV99S
BAT64-04W	BAT760	BAV23A	BAV99W
BAT64-05	BAT81	BAV23C	BAW101
BAT64-05W	BAT82	BAV23S	BAW101S
BAT64-06	BAT83	BAV45	BAW156
BAT64-06W	BAT85	BAV70	BAW56
BAT65	BAT854AW	BAV70DXV6T5G	BAW56LT1
BAT66-05	BAT854CW	BAV70LT1	BAW56LT1G
BAT68	BAT854SW	BAV70LT1G	BAW56LT3G
BAT68-04	BAT854W	BAV70LT3G	BAW56M
BAT68-04W	BAT86	BAV70M	BAW56M3T5G

Multisim 14.0 Power Pro Components

BAW56S	BB515	BB833	BBY57-02V
BAW56T	BB535	BB837	BBY57-02W
BAW56TT1G	BB545	BB857	BBY57-05W
BAW56W	BB555	BB909A	BBY58-02V
BAW62	BB555-02V	BB909B	BBY58-02W
BAW78D	BB565	BB910	BBY58-03W
BAX12	BB565-02V	BB911	BBY58-05W
BAX14	BB619	BB914	BBY58-06W
BAX18	BB620	BBY31	BBY62
BAY80	BB629	BBY39	BBY65-02V
BB112	BB639	BBY40	BBY66-02V
BB119	BB639C	BBY42	BBY66-05W
BB130	BB640	BBY51-02W	BC107BP
BB204B	BB644	BBY51-03W	BC108BP
BB204G	BB659	BBY52-02L	BC109BP
BB212	BB659C	BBY52-02W	BC177AP
BB215	BB659C-02V	BBY53-02L	BC178AP
BB219	BB664	BBY53-02V	BC182BP
BB240	BB664-02V	BBY53-02W	BC183BP
BB241	BB689	BBY53-03W	BC184BP
BB249	BB689-02V	BBY53-05W	BC212AP
BB405B	BB804	BBY55-02V	BC213AP
BB417	BB809	BBY55-03W	BC237BP
BB439	BB811	BBY56-02W	BC238BP
BB512	BB814	BBY56-03W	BC239BP

Multisim 14.0 Power Pro Components

BC264A	BC52PA	BC557A	BC807
BC264B	BC53-10PA	BC557AP	BC807-16
BC264C	BC53-16PA	BC557B	BC807-16LT1G
BC264D	BC53PA	BC557BG	BC807-16LT3G
BC307AP	BC54-10PA	BC557BRL1G	BC807-16W
BC308AP	BC54-16PA	BC557BZL1G	BC807-25
BC327	BC546BP	BC558AP	BC807-25LT1G
BC328	BC547A	BC558B	BC807-25LT3G
BC337	BC547B	BC559AP	BC807-25QA
BC337AP	BC547BG	BC55PA	BC807-25W
BC338	BC547BP	BC560AP	BC807-40
BC338AP	BC547BRL1G	BC56-10PA	BC807-40LT1G
BC368	BC547BZL1G	BC56-16PA	BC807-40LT3G
BC369	BC547C	BC56PA	BC807-40QA
BC372	BC548A	BC635	BC807-40W
BC373	BC548B	BC636	BC807DS
BC413BP	BC548BP	BC637	BC807W
BC414BP	BC548C	BC638	BC808-16
BC415AP	BC549BP	BC639	BC808-25
BC416AP	BC54PA	BC640	BC808-40
BC51-10PA	BC550BP	BC68-25PA	BC817
BC51-16PA	BC55-10PA	BC68PA	BC817-16
BC51PA	BC55-16PA	BC69-16PA	BC817-16W
BC52-10PA	BC556AP	BC69-25PA	BC817-25
BC52-16PA	BC556B	BC69PA	BC817-25LT1

Multisim 14.0 Power Pro Components

BC817-25LT1G	BC846BPN	BC847BPN	BC849CW
BC817-25LT3G	BC846BS	BC847BS	BC850B
BC817-25QA	BC846BT	BC847BT	BC850BW
BC817-25W	BC846BW	BC847BV	BC850C
BC817-40	BC846DS	BC847BVN	BC850CW
BC817-40QA	BC846S	BC847BW	BC856
BC817-40W	BC846T	BC847C	BC856A
BC817DPN	BC846W	BC847CDXV6T1G	BC856ALT1G
BC817DS	BC847	BC847CM	BC856AT
BC817W	BC847A	BC847CMB	BC856AW
BC818-16	BC847AM	BC847CT	BC856B
BC818-25	BC847AMB	BC847CTT1G	BC856BDW1T1G
BC818-40	BC847AT	BC847CW	BC856BDW1T3G
BC846	BC847AW	BC847DS	BC856BS
BC846A	BC847B	BC847T	BC856BT
BC846ALT1G	BC847BDW1T1G	BC847W	BC856BW
BC846ALT3G	BC847BDW1T3	BC848	BC856BWT1G
BC846AT	BC847BDW1T3G	BC848A	BC856S
BC846AW	BC847BM	BC848B	BC856T
BC846B	BC847BMB	BC848BW	BC856W
BC846BDW1T1G	BC847BPDW1T1	BC848CW	BC857
BC846BLT1G	BC847BPDW1T1G	BC848W	BC857A
BC846BLT3G	BC847BPDW1T2G	BC849B	BC857AM
BC846BMB	BC847BPDW1T3G	BC849BW	BC857AMB
BC846BPDW1T1G	BC847BPDXV6T1G	BC849C	BC857AT

Multisim 14.0 Power Pro Components

BC857AW	BC859B	BCP49	BCP56T1G
BC857B	BC859BW	BCP51	BCP56T3G
BC857BDW1T1G	BC859C	BCP51-10	BCP68
BC857BM	BC859CW	BCP51-16	BCP68-25
BC857BMB	BC860A	BCP52	BCP68T1G
BC857BS	BC860B	BCP52-10	BCP69
BC857BT	BC860BW	BCP52-16	BCP69-16
BC857BV	BC860C	BCP53	BCP69-25
BC857BW	BC860CW	BCP53-10	BCP69T1G
BC857C	BC868	BCP53-16	BCR08PN
BC857CM	BC868-25	BCP54	BCR108
BC857CMB	BC869	BCP54-10	BCR108S
BC857CT	BC869-16	BCP54-16	BCR108W
BC857CW	BC869-25	BCP55	BCR10PN
BC857T	BCD_7SEG_DCD	BCP55-10	BCR112
BC857W	BCM61B	BCP55-16	BCR112W
BC858	BCM62B	BCP56	BCR116
BC858A	BCM847BS	BCP56-10	BCR116S
BC858AW	BCM847BV	BCP56-10T1	BCR116W
BC858B	BCM847DS	BCP56-10T1G	BCR119
BC858BW	BCM856BS	BCP56-16	BCR119S
BC858C	BCM856DS	BCP56-16T1	BCR119W
BC858CW	BCM857BS	BCP56-16T1G	BCR129
BC858W	BCM857BV	BCP56-16T3G	BCR129W
BC859A	BCM857DS	BCP56T1	BCR133

Multisim 14.0 Power Pro Components

BCR133S	BCR185	BCR573	BCW30
BCR133W	BCR185S	BCR583	BCW31
BCR135	BCR185W	BCV26	BCW32
BCR135S	BCR191	BCV27	BCW33
BCR135W	BCR191W	BCV28	BCW60A
BCR141	BCR192	BCV29	BCW60B
BCR141S	BCR192W	BCV46	BCW60C
BCR141W	BCR196	BCV47	BCW60D
BCR142	BCR196W	BCV48	BCW60FF
BCR142W	BCR198	BCV49	BCW60FN
BCR146	BCR198S	BCV61	BCW61A
BCR148	BCR198W	BCV61A	BCW61B
BCR148S	BCR22PN	BCV61B	BCW61C
BCR148W	BCR35PN	BCV61C	BCW61D
BCR158	BCR48PN	BCV62	BCW61FF
BCR158W	BCR503	BCV62A	BCW61FN
BCR162	BCR505	BCV62B	BCW65A
BCR166	BCR512	BCV62C	BCW65B
BCR166W	BCR521	BCV63	BCW65C
BCR169	BCR523	BCV63B	BCW66F
BCR169S	BCR523U	BCV64B	BCW66G
BCR169W	BCR533	BCV65	BCW66H
BCR183	BCR553	BCV71	BCW67A
BCR183S	BCR555	BCV72	BCW68
BCR183W	BCR562	BCW29	BCW68F

Multisim 14.0 Power Pro Components

BCW69	BCX55	BD135G	BD243C
BCW70	BCX55-10	BD136	BD243CG
BCW71	BCX55-16	BD136G	BD244B
BCW72	BCX56	BD137	BD244BG
BCW89	BCX56-10	BD137G	BD244C
BCX17	BCX56-16	BD138	BD244CG
BCX17_25	BCX58IX	BD138G	BD329
BCX17LT1G	BCX58VIII	BD139	BD330
BCX18	BCX58X	BD139G	BD436TG
BCX19	BCX59IX	BD140	BD437
BCX38B	BCX59VIII	BD140G	BD437G
BCX41	BCX59X	BD159G	BD437TG
BCX42	BCX68	BD179G	BD438G
BCX51	BCX69	BD180G	BD439G
BCX51-10	BCX70G	BD234G	BD440G
BCX51-16	BCX70H	BD237	BD441
BCX52	BCX70J	BD237G	BD441G
BCX52-10	BCX70K	BD241B	BD442G
BCX52-16	BCX71G	BD241C	BD533
BCX53	BCX71H	BD241CG	BD534
BCX53-10	BCX71J	BD242B	BD535
BCX53-16	BCX71K	BD242BG	BD536
BCX54	BD135	BD242C	BD537
BCX54-10	BD135-10	BD242CG	BD538
BCX54-16	BD135-16	BD243B	BD675AG

Multisim 14.0 Power Pro Components

BD675G	BDV64BG	BF410C	BF620
BD676AG	BDV65BG	BF410D	BF621
BD676G	BDW42G	BF420	BF622
BD677AG	BDW46G	BF421	BF623
BD677G	BDW47G	BF422	BF720
BD678AG	BDX33BG	BF422G	BF721
BD678G	BDX33CG	BF423	BF722
BD679AG	BDX34BG	BF450	BF723
BD679G	BDX34CG	BF469	BF799
BD680AG	BDX53BG	BF470	BF799W
BD680G	BDX53CG	BF471	BF820
BD681G	BDX54BG	BF472	BF820W
BD682G	BDX54CG	BF510	BF821
BD787G	BF240	BF511	BF822
BD788G	BF245A	BF512	BF822W
BD801	BF245B	BF513	BF823
BD802	BF245C	BF517	BF824
BD809G	BF246A	BF545A	BF824W
BD810G	BF247A	BF545B	BF840
BDP947	BF256A	BF545C	BF851A
BDP948	BF256B	BF550	BF851B
BDP949	BF256C	BF556A	BF851C
BDP950	BF370R	BF556B	BF861A
BDP953	BF410A	BF570	BF861B
BDP954	BF410B	BF603	BF861C

Multisim 14.0 Power Pro Components

BF869	BFN24	BFP280	BFR31
BF871	BFN25	BFP280W	BFR35AP
BF904	BFN26	BFP405	BFR92ALT1
BF904R	BFN27	BFP420	BFR92P
BF904WR	BFN36	BFP450	BFR92W
BF908WR	BFN37	BFP490	BFR93A
BF909	BFN39	BFP81	BFR93ALT1
BF909R	BFP136W	BFP93A	BFR93AW
BF909WR	BFP180	BFQ31	BFS17
BF998	BFP180W	BFQ81	BFS17H
BF998R	BFP181	BFR106	BFS17LT1
BF998WR	BFP181W	BFR180	BFS17P
BFG135A	BFP182	BFR180W	BFS17S
BFG193	BFP182W	BFR181	BFS17W
BFG194	BFP183	BFR181W	BFS18
BFG196	BFP183W	BFR182	BFS19
BFG19S	BFP193	BFR182W	BFS20
BFG235	BFP193W	BFR183	BFS20W
BFN16	BFP194	BFR183W	BFS480
BFN17	BFP196	BFR193	BFS481
BFN18	BFP196W	BFR193W	BFS482
BFN19	BFP22	BFR194	BFS483
BFN21	BFP23	BFR280	BFS60
BFN22	BFP25	BFR280W	BFT46
BFN23	BFP26	BFR30	BFT92

Multisim 14.0 Power Pro Components

BFT92W	BOOSTDCM	BSB028N06NN3 G	BSC018NE2LSI
BFU308	BOOSTVM	BSB044N08NN3 G	BSC019N02KS G
BFU309	BOSCH-EDC16-BDM-HDR	BSB056N10NN3 G	BSC019N04LS
BFU310	BPASS	BSB165N15NZ3 G	BSC019N04NS G
BFW10	BPV10NF	BSB280N15NZ3 G	BSC020N03LS G
BFW11	BPV22NF	BSC009NE2LS	BSC020N03MS G
BFW12	BPV23F	BSC010N04LS	BSC022N04LS
BFW13	BPV23NF	BSC010N04LSI	BSC024NE2LS
BFW61	BPW 34	BSC010NE2LS	BSC025N03LS G
BICOLOR_LED_Red/Green	BPW 34 FA	BSC010NE2LSI	BSC025N03MS G
BICOLOR_LED_Red-Orange/Green	BPW 34 FAS	BSC011N03LS	BSC026N02KS G
BIPOLAR_CURRENT	BPW 34 FASR	BSC011N03LSI	BSC026N04LS
BIPOLAR_VOLTAGE	BRUSHLESS_DC_MACHINE	BSC014N03LS G	BSC027N04LS G
BJT_LPNP	BRUSHLESS_DC_MACHINE_HALL	BSC014N03MS G	BSC028N06LS3 G
BJT_NPN	BS170	BSC014N04LS	BSC028N06NS
BJT_NPN_4T	BSB008NE2LX	BSC014N04LSI	BSC030N03LS G
BJT_NPN_RATED	BSB012N03LX3 G	BSC014N06NS	BSC030N03MS G
BJT_PNP	BSB012NE2LX	BSC014NE2LSI	BSC030N04NS G
BJT_PNP_4T	BSB012NE2LXI	BSC016N03LS G	BSC030P03NS3 G
BJT_PNP_RATED	BSB013NE2LXI	BSC016N03MS G	BSC031N06NS3 G
BOOST_CONVERTER	BSB014N04LX3 G	BSC016N04LS G	BSC032N04LS
BOOSTCCM	BSB015N04NX3 G	BSC016N06NS	BSC032NE2LS
BOOSTCM	BSB017N03LX3 G	BSC017N04NS G	BSC034N06NS
		BSC018NE2LS	BSC035N04LS G
			BSC036NE7NS3 G

Multisim 14.0 Power Pro Components

BSC039N06NS	BSC079N10NS G	BSC100N03LS G	BSC240N12NS3 G
BSC042N03LS G	BSC080N03LS G	BSC100N03MS G	BSC252N10NSF G
BSC042N03MS G	BSC080N03MS G	BSC100N06LS3 G	BSC265N10LSF G
BSC042NE7NS3 G	BSC080P03LS G	BSC100N10NSF G	BSC320N20NS3 G
BSC046N02KS G	BSC082N10LS G	BSC105N10LSF G	BSC340N08NS3 G
BSC046N10NS3 G	BSC084P03NS3 G	BSC109N10NS3 G	BSC360N15NS3 G
BSC047N08NS3 G	BSC084P03NS3E G	BSC110N06NS3 G	BSC440N10NS3 G
BSC050N03LS G	BSC0901NS	BSC118N10NS G	BSC500N20NS3 G
BSC050N03MS G	BSC0901NSI	BSC120N03LS G	BSC520N15NS3 G
BSC050N04LS G	BSC0902NS	BSC120N03MS G	BSC600N25NS3 G
BSC050NE2LS	BSC0902NSI	BSC123N08NS3 G	BSC750N10ND G
BSC052N03LS	BSC0904NSI	BSC123N10LS G	BSC900N20NS3 G
BSC054N04NS G	BSC0906NS	BSC12DN20NS3 G	BSD214
BSC057N03LS G	BSC0908NS	BSC130P03LS G	BSD214SN
BSC057N03MS G	BSC0909NS	BSC150N03LD G	BSD215
BSC057N08NS3 G	BSC090N03LS G	BSC152N10NSF G	BSD223P
BSC059N04LS G	BSC090N03MS G	BSC159N10LSF G	BSD235N
BSC060N10NS3 G	BSC0910NDI	BSC160N10NS3 G	BSD314SPE
BSC060P03NS3E G	BSC0911ND	BSC16DN25NS3 G	BSD316SN
BSC066N06NS	BSC0921NDI	BSC190N12NS3 G	BSD816SN
BSC067N06LS3 G	BSC0923NDI	BSC190N15NS3 G	BSD840N
BSC070N10NS3 G	BSC0924NDI	BSC196N10NS G	BSE-080-01-L-D-A
BSC072N03LD G	BSC0925ND	BSC200P03LS G	BSF024N03LT3 G
BSC076N06NS3 G	BSC093N04LS G	BSC205N10LS G	BSF030NE2LQ
BSC077N12NS3 G	BSC097N06NS	BSC22DN20NS3 G	BSF035NE2LQ

Multisim 14.0 Power Pro Components

BSF050N03LQ3 G	BSL307SP	BSO200P03S H	BSP171
BSF134N10NJ3 G	BSL308PE	BSO201SP H	BSP171P
BSF450NE7NH3 G	BSL314PE	BSO203SP H	BSP19
BSH103	BSL606SN	BSO207P H	BSP19AT1G
BSH105	BSL802SN	BSO211P H	BSP204
BSH108	BSL806N	BSO220N03MD G	BSP204A
BSH111	BSN011NE2LS	BSO220N03MS G	BSP205
BSH114	BSN011NE2LSI	BSO301SP H	BSP206
BSH121	BSN012N03LS	BSO303SP H	BSP220
BSH201	BSN012N03LSI	BSO330N02K G	BSP225
BSH202	BSN045NE2LS	BSO613SPV G	BSP230
BSH203	BSN048N03LS	BSP 60 E6327	BSP250
BSH205	BSN20	BSP030	BSP295
BSH207	BSO033N03MS G	BSP100	BSP296
BSJ108	BSO040N03MS G	BSP110	BSP297
BSJ109	BSO051N03MS G	BSP122	BSP299
BSJ110	BSO065N03MS G	BSP123	BSP304
BSL202SN	BSO080P03NS3 G	BSP125	BSP304A
BSL205N	BSO080P03NS3E G	BSP126	BSP31
BSL207N	BSO080P03S H	BSP129	BSP315
BSL207SP	BSO083N03MS G	BSP130	BSP315P
BSL211SP	BSO110N03MS G	BSP135	BSP316
BSL214N	BSO130N03MS G	BSP149	BSP316P
BSL302SN	BSO130P03S H	BSP16T1G	BSP317
BSL306N	BSO150N03MD G	BSP170P	BSP317P

Multisim 14.0 Power Pro Components

BSP318S	BSR302N	BSS138	BSS296
BSP319	BSR31	BSS138BK	BSS297
BSP32	BSR315P	BSS138BKS	BSS306N
BSP324	BSR316P	BSS138BKW	BSS308PE
BSP33	BSR33	BSS138LT1G	BSS314PE
BSP41	BSR41	BSS138LT3G	BSS315P
BSP43	BSR43	BSS138N	BSS316N
BSP50	BSR56	BSS138P	BSS606N
BSP51	BSR57	BSS138PS	BSS63
BSP52	BSR58	BSS138PW	BSS64
BSP52T1G	BSR606N	BSS138W	BSS670S2L
BSP52T3G	BSR802N	BSS139	BSS7728N
BSP60	BSR92P	BSS145	BSS79B
BSP61	BSS100	BSS159N	BSS79C
BSP613P	BSS101	BSS169	BSS806N
BSP62	BSS110	BSS192	BSS80B
BSP88	BSS119	BSS192P	BSS80C
BSP89	BSS123	BSS205N	BSS816NW
BSP92P	BSS123LT1G	BSS209PW	BSS81B
BSR13	BSS125	BSS214N	BSS81C
BSR14	BSS126	BSS214NW	BSS82B
BSR16	BSS127	BSS223PW	BSS82C
BSR19A	BSS129	BSS225	BSS83
BSR202N	BSS131	BSS229	BSS83P
BSR30	BSS135	BSS295	BSS84

Multisim 14.0 Power Pro Components

BSS84AK	BST61	BSZ058N03MS G	BSZ120P03NS3 G
BSS84AKM	BST62	BSZ060NE2LS	BSZ120P03NS3E G
BSS84AKMB	BST76A	BSZ065N03LS	BSZ123N08NS3 G
BSS84AKS	BST82	BSZ067N06LS3 G	BSZ12DN20NS3 G
BSS84AKT	BSV236SP	BSZ068N06NS	BSZ130N03LS G
BSS84AKV	BSV52	BSZ076N06NS3 G	BSZ130N03MS G
BSS84AKW	BSV78	BSZ086P03NS3 G	BSZ150N10LS3 G
BSS84LT1G	BSV79	BSZ086P03NS3E G	BSZ160N10NS3 G
BSS84P	BSV80	BSZ088N03LS G	BSZ165N04NS G
BSS84PW	BSV81	BSZ088N03MS G	BSZ16DN25NS3 G
BSS84PW H6327	BSZ018NE2LS	BSZ0901NS	BSZ180P03NS3 G
BSS87	BSZ018NE2LSI	BSZ0901NSI	BSZ180P03NS3E G
BSS88	BSZ019N03LS	BSZ0902NS	BSZ22DN20NS3 G
BSS89	BSZ023N04LS	BSZ0902NSI	BSZ240N12NS3 G
BSS92	BSZ028N04LS	BSZ0904NSI	BSZ340N08NS3 G
BSS98	BSZ034N04LS	BSZ0907ND	BSZ42DN25NS3 G
BST100	BSZ035N03LS G	BSZ0908ND	BSZ440N10NS3 G
BST110	BSZ035N03MS G	BSZ0909NS	BSZ520N15NS3 G
BST120	BSZ036NE2LS	BSZ097N04LS G	BSZ900N15NS3 G
BST122	BSZ040N04LS G	BSZ100N03LS G	BSZ900N20NS3 G
BST39	BSZ042N04NS G	BSZ100N03MS G	BT134
BST50	BSZ042N06NS	BSZ100N06LS3 G	BT134-E
BST51	BSZ050N03LS G	BSZ100N06NS	BT134-F
BST52	BSZ050N03MS G	BSZ105N04NS G	BT134-G
BST60	BSZ058N03LS G	BSZ110N06NS3 G	BT134W

Multisim 14.0 Power Pro Components

BT136	BTA140	BTW48_800	BUF602ID
BT136-E	BTW30_1000	BTY79_400R	BUF602IDBVR
BT136-F	BTW30_1200	BTY91_400R	BUF634F
BT136-G	BTW30_600	BU323ZG	BUF634P
BT137	BTW30_800	BU406G	BUF634T
BT137-E	BTW38_600R	BUB323ZG	BUF634U
BT137-F	BTW39_100	BUB323ZT4G	BUFFER
BT137-G	BTW39_1100	BUCK_BOOST_CONVERTER	BUH100G
BT138	BTW39_1200	BUCK_CONVERTER	BUH150G
BT138-E	BTW39_200	BUCKCCM	BUH50G
BT138-F	BTW39_300	BUCKCM	BUK6207-55C
BT138-G	BTW39_400	BUCKDCM	BUK6209-30C
BT139	BTW39_50	BUCKVM	BUK6210-55C
BT139-E	BTW39_600	BUD42D-1G	BUK6211-75C
BT139-F	BTW39_700	BUD42DT4G	BUK6212-40C
BT139-G	BTW39_800	BUF	BUK6213-30C
BT145_500R	BTW39_900	BUF_3S_AHOE	BUK6215-75C
BT148_400R	BTW40_400R	BUF_3S_ALOE	BUK6217-55C
BT148W_400R	BTW42_600R	BUF_CO	BUK6218-40C
BT149_B	BTW43	BUF_INV	BUK6226-75C
BT150_500R	BTW45_400R	BUF600AP	BUK6228-55C
BT151_500R	BTW48_1200	BUF600AU	BUK6246-75C
BT152_400R	BTW48_200	BUF601AP	BUK624R5-30C
BT153_500R	BTW48_400	BUF601AU	BUK625R0-40C
BT169_B	BTW48_600		BUK625R2-30C

Multisim 14.0 Power Pro Components

BUK626R2-40C	BUK663R7-75C	BUK764R2-80E	BUK7Y12-100E
BUK6507-55C	BUK664R4-55C	BUK765R0-100E	BUK7Y12-40E
BUK6507-75C	BUK664R6-40C	BUK768R1-100E	BUK7Y12-55B
BUK6510-75C	BUK6C2R1-55C	BUK769R6-80E	BUK7Y13-40B
BUK652R1-30C	BUK6C3R3-75C	BUK7E13-60E	BUK7Y14-80E
BUK652R6-40C	BUK7514-60E	BUK7E1R6-30E	BUK7Y15-100E
BUK653R3-30C	BUK751R6-30E	BUK7E1R8-40E	BUK7Y153-100E
BUK653R4-40C	BUK751R8-40E	BUK7E1R9-40E	BUK7Y15-60E
BUK653R5-55C	BUK752R3-40E	BUK7E2R3-40E	BUK7Y18-55B
BUK653R7-30C	BUK752R7-60E	BUK7E2R6-60E	BUK7Y18-75B
BUK654R0-75C	BUK753R1-40E	BUK7E3R1-40E	BUK7Y20-30B
BUK654R6-55C	BUK753R5-60E	BUK7E3R5-60E	BUK7Y21-40E
BUK654R8-40C	BUK753R8-80E	BUK7E4R0-80E	BUK7Y22-100E
BUK655R0-75C	BUK754R0-40C	BUK7E4R6-60E	BUK7Y25-40B
BUK6607-55C	BUK754R7-60E	BUK7E5R2-100E	BUK7Y25-60E
BUK6607-75C	BUK755R4-100E	BUK7E8R3-40E	BUK7Y25-80E
BUK6610-75C	BUK758R3-40E	BUK7K25-40E	BUK7Y28-75B
BUK661R8-30C	BUK7613-100E	BUK7K5R1-30E	BUK7Y29-40E
BUK661R9-40C	BUK761R3-30E	BUK7K5R6-30E	BUK7Y35-55B
BUK662R4-40C	BUK761R4-30E	BUK7K6R8-40E	BUK7Y38-100E
BUK662R5-30C	BUK761R5-40E	BUK7Y07-30B	BUK7Y41-80E
BUK662R7-55C	BUK761R6-40E	BUK7Y08-40B	BUK7Y43-60E
BUK663R2-40C	BUK762R4-60E	BUK7Y102-100B	BUK7Y4R4-40E
BUK663R5-30C	BUK7631-100E	BUK7Y10-30B	BUK7Y4R8-60E
BUK663R5-55C	BUK763R8-80E	BUK7Y113-100E	BUK7Y53-100B

Multisim 14.0 Power Pro Components

BUK7Y54-75B	BUK9637-100E	BUK9Y11-30B	BUK9Y43-60E
BUK7Y59-60E	BUK964R2-80E	BUK9Y113-100E	BUK9Y4R4-40E
BUK7Y65-100E	BUK964R7-80E	BUK9Y11-80E	BUK9Y4R8-60E
BUK7Y6R0-60E	BUK965R8-100E	BUK9Y12-100E	BUK9Y53-100B
BUK7Y72-80E	BUK969R3-100E	BUK9Y12-40E	BUK9Y58-75B
BUK7Y7R6-40E	BUK9E15-60E	BUK9Y12-55B	BUK9Y59-60E
BUK7Y7R8-80E	BUK9E1R6-30E	BUK9Y14-40B	BUK9Y65-100E
BUK7Y8R7-60E	BUK9E2R3-40E	BUK9Y14-80E	BUK9Y6R0-60E
BUK7Y98-80E	BUK9E2R8-60E	BUK9Y15-100E	BUK9Y72-80E
BUK7Y9R9-80E	BUK9E3R7-60E	BUK9Y153-100E	BUK9Y7R6-40E
BUK9515-60E	BUK9E4R4-80E	BUK9Y15-60E	BUK9Y8R5-80E
BUK951R6-30E	BUK9E4R9-60E	BUK9Y19-55B	BUK9Y8R7-60E
BUK951R9-40E	BUK9E6R1-100E	BUK9Y19-75B	BUL146
BUK952R3-40E	BUK9E8R5-40E	BUK9Y21-40E	BUL45D2G
BUK952R8-60E	BUK9K18-40E	BUK9Y22-100E	BUL45G
BUK953R2-40E	BUK9K29-100E	BUK9Y22-30B	BUV21G
BUK953R5-60E	BUK9K35-60E	BUK9Y25-60E	BUV22
BUK954R4-80E	BUK9K45-100E	BUK9Y25-80E	BUV22G
BUK958R5-40E	BUK9K52-60E	BUK9Y27-40B	BUV26G
BUK9611-80E	BUK9K6R2-40E	BUK9Y29-40E	BUW41
BUK9615-100E	BUK9K89-100E	BUK9Y30-75B	BUW41A
BUK961R4-30E	BUK9Y07-30B	BUK9Y38-100E	BUW64A
BUK961R5-30E	BUK9Y09-40B	BUK9Y3R0-40E	BUW64B
BUK961R6-40E	BUK9Y104-100B	BUK9Y40-55B	BUW64C
BUK962R5-60E	BUK9Y107-80E	BUK9Y41-80E	BUX11A

Multisim 14.0 Power Pro Components

BUX14	BUZ173	BUZ356	BUZ80A
BUX21	BUZ20	BUZ358	BUZ81
BUX32	BUZ21	BUZ40B	BUZ84A
BUX32A	BUZ22	BUZ41A	BUZ90
BUX32B	BUZ220	BUZ45B	BUZ91A
BUX33	BUZ271	BUZ50B	BUZ92
BUX33A	BUZ272	BUZ51	BUZZER
BUX33B	BUZ305	BUZ53A	BVSS123LT1G
BUX85G	BUZ30A	BUZ60	BVSS138LT1G
BUY69A	BUZ31	BUZ61A	BY228
BUY69B	BUZ310	BUZ64	BY328
BUY69C	BUZ311	BUZ70	BY438
BUZ10	BUZ323	BUZ71	BY448
BUZ100	BUZ325	BUZ71A	BY458
BUZ101	BUZ326	BUZ71L	BY505
BUZ102	BUZ331	BUZ71LGE	BY527
BUZ104	BUZ334	BUZ72	BY584
BUZ10L	BUZ338	BUZ72GE	BY627
BUZ10M	BUZ341	BUZ73	BY705
BUZ11	BUZ342	BUZ73AGE	BY706
BUZ11A	BUZ342KL	BUZ73L	BY710
BUZ11GE	BUZ344	BUZ74A	BY711
BUZ12	BUZ345	BUZ76	BY712
BUZ12AL	BUZ346	BUZ77A	BY713
BUZ171	BUZ350	BUZ78	BY714

Multisim 14.0 Power Pro Components

BY715	BYD17D	BYD73C	BYM10-100
BY716	BYD17G	BYD73D	BYM10-1000
BY717	BYD17J	BYD73E	BYM10-1000-E3/97
BY718	BYD17K	BYD73F	BYM10-200
BY719	BYD17M	BYD73G	BYM10-400
BY720	BYD31D	BYD74A	BYM10-50
BY721	BYD31G	BYD74B	BYM10-600
BY722	BYD31J	BYD74C	BYM10-800
BY723	BYD33D	BYD74D	BYM11-100
BYD11	BYD33G	BYD74E	BYM11-1000
BYD11D	BYD33J	BYD74F	BYM11-1000-E3/96
BYD11G	BYD33K	BYD74G	BYM11-100-E3/96
BYD11J	BYD33M	BYD77A	BYM11-200
BYD11K	BYD34D	BYD77B	BYM11-400
BYD11M	BYD34G	BYD77C	BYM11-50
BYD13D	BYD34J	BYD77D	BYM11-600
BYD13G	BYD34K	BYD77E	BYM11-800
BYD13J	BYD34M	BYD77F	BYM12-400-E3/96
BYD13K	BYD37D	BYD77G	BYM26A
BYD13M	BYD37G	BYG10G-E3/TR	BYM26B
BYD14D	BYD37J	BYG10J-E3/TR	BYM26C
BYD14G	BYD37K	BYG20J-E3/TR	BYM26D
BYD14J	BYD37M	BYG21M-E3/TR	BYM26E
BYD14K	BYD73A	BYG22D-E3/TR	BYM36A
BYD14M	BYD73B	BYG24J-E3/TR3	BYM36B

Multisim 14.0 Power Pro Components

BYM36C	BYV32-200G	BZA418A	BZB784-C15
BYM36D	BYV36A	BZA420A	BZB784-C2V4
BYM36E	BYV36B	BZA456A	BZB784-C2V7
BYM56A	BYV36C	BZA462A	BZB784-C3V0
BYM56B	BYV36D	BZA820A	BZB784-C3V3
BYM56C	BYV36E	BZA856A	BZB784-C3V6
BYM56D	BYV95A	BZA856AL	BZB784-C3V9
BYM56E	BYV95B	BZA856AVL	BZB784-C4V3
BYS10-45-E3/TR	BYV95C	BZA862A	BZB784-C4V7
BYS11-90-E3/TR	BYV96D	BZA862AL	BZB784-C5V1
BYT28-300-E3/45	BYV96E	BZA862AVL	BZB784-C5V6
BYV10-20	BYW29-200G	BZA868A	BZB784-C6V2
BYV10-30	BYW51-200G	BZA868AL	BZB784-C6V8
BYV10-40	BYW54	BZA868AVL	BZB784-C7V5
BYV26A	BYW55	BZA956A	BZB784-C8V2
BYV26B	BYW56	BZA956AVL	BZB784-C9V1
BYV26C	BYW80-200G	BZA962A	BZB84-B10
BYV26D	BYW95A	BZA962AVL	BZB84-B11
BYV26E	BYW95B	BZA968A	BZB84-B12
BYV27-100	BYW95C	BZA968AVL	BZB84-B13
BYV27-50	BYW96D	BZB100A	BZB84-B15
BYV28-100	BYW96E	BZB784-C10	BZB84-B16
BYV28-150	BYX10G	BZB784-C11	BZB84-B18
BYV28-200	BYX110GP	BZB784-C12	BZB84-B20
BYV28-50	BZA408B	BZB784-C13	BZB84-B22

Multisim 14.0 Power Pro Components

BZB84-B24	BZB84-B7V5	BZB84-C47	BZB984-C3V9
BZB84-B27	BZB84-B8V2	BZB84-C4V3	BZB984-C4V3
BZB84-B2V4	BZB84-B9V1	BZB84-C4V7	BZB984-C4V7
BZB84-B2V7	BZB84-C10	BZB84-C51	BZB984-C5V1
BZB84-B30	BZB84-C11	BZB84-C56	BZB984-C5V6
BZB84-B33	BZB84-C12	BZB84-C5V1	BZB984-C6V2
BZB84-B36	BZB84-C13	BZB84-C5V6	BZB984-C6V8
BZB84-B39	BZB84-C15	BZB84-C62	BZB984-C7V5
BZB84-B3V0	BZB84-C16	BZB84-C68	BZB984-C8V2
BZB84-B3V3	BZB84-C18	BZB84-C6V2	BZB984-C9V1
BZB84-B3V6	BZB84-C20	BZB84-C6V8	BZT52H-B10
BZB84-B3V9	BZB84-C22	BZB84-C75	BZT52H-B11
BZB84-B43	BZB84-C24	BZB84-C7V5	BZT52H-B12
BZB84-B47	BZB84-C27	BZB84-C8V2	BZT52H-B13
BZB84-B4V3	BZB84-C2V4	BZB84-C9V1	BZT52H-B15
BZB84-B4V7	BZB84-C2V7	BZB984-C10	BZT52H-B16
BZB84-B51	BZB84-C30	BZB984-C11	BZT52H-B18
BZB84-B56	BZB84-C33	BZB984-C12	BZT52H-B20
BZB84-B5V1	BZB84-C36	BZB984-C13	BZT52H-B22
BZB84-B5V6	BZB84-C39	BZB984-C15	BZT52H-B24
BZB84-B62	BZB84-C3V0	BZB984-C2V4	BZT52H-B27
BZB84-B68	BZB84-C3V3	BZB984-C2V7	BZT52H-B2V4
BZB84-B6V2	BZB84-C3V6	BZB984-C3V0	BZT52H-B2V7
BZB84-B6V8	BZB84-C3V9	BZB984-C3V3	BZT52H-B30
BZB84-B75	BZB84-C43	BZB984-C3V6	BZT52H-B33

Multisim 14.0 Power Pro Components

BZT52H-B36	BZT52H-C22	BZT52H-C7V5	BZV55-B3V6
BZT52H-B39	BZT52H-C24	BZT52H-C8V2	BZV55-B3V9
BZT52H-B3V0	BZT52H-C27	BZT52H-C9V1	BZV55-B43
BZT52H-B43	BZT52H-C2V4	BZV49-C12	BZV55-B47
BZT52H-B47	BZT52H-C2V7	BZV49-C16	BZV55-B4V3
BZT52H-B51	BZT52H-C30	BZV49-C3V6	BZV55-B4V7
BZT52H-B56	BZT52H-C33	BZV55-B10	BZV55-B51
BZT52H-B5V1	BZT52H-C36	BZV55-B11	BZV55-B56
BZT52H-B5V6	BZT52H-C39	BZV55-B12	BZV55-B5V1
BZT52H-B62	BZT52H-C3V0	BZV55-B13	BZV55-B5V6
BZT52H-B68	BZT52H-C3V6	BZV55-B15	BZV55-B68
BZT52H-B6V2	BZT52H-C3V9	BZV55-B16	BZV55-B6V2
BZT52H-B6V8	BZT52H-C43	BZV55-B18	BZV55-B6V8
BZT52H-B75	BZT52H-C47	BZV55-B20	BZV55-B75
BZT52H-B7V5	BZT52H-C4V3	BZV55-B22	BZV55-B7V5
BZT52H-B8V2	BZT52H-C4V7	BZV55-B24	BZV55-B8V2
BZT52H-B9V1	BZT52H-C51	BZV55-B27	BZV55-B9V1
BZT52H-C10	BZT52H-C56	BZV55-B2V4	BZV55-C10
BZT52H-C11	BZT52H-C5V1	BZV55-B2V7	BZV55-C11
BZT52H-C12	BZT52H-C5V6	BZV55-B30	BZV55-C12
BZT52H-C13	BZT52H-C62	BZV55-B33	BZV55-C13
BZT52H-C15	BZT52H-C68	BZV55-B36	BZV55-C15
BZT52H-C16	BZT52H-C6V2	BZV55-B39	BZV55-C16
BZT52H-C18	BZT52H-C6V8	BZV55-B3V0	BZV55-C18
BZT52H-C20	BZT52H-C75	BZV55-B3V3	BZV55-C27

Multisim 14.0 Power Pro Components

BZV55-C2V4	BZV60-B18	BZV60-B6V2	BZV60-C3V6
BZV55-C2V7	BZV60-B20	BZV60-B6V8	BZV60-C3V9
BZV55-C33	BZV60-B22	BZV60-B75	BZV60-C43
BZV55-C3V0	BZV60-B24	BZV60-B7V5	BZV60-C47
BZV55-C3V3	BZV60-B27	BZV60-B8V2	BZV60-C4V3
BZV55-C3V6	BZV60-B2V4	BZV60-B9V1	BZV60-C4V7
BZV55-C3V9	BZV60-B2V7	BZV60-C10	BZV60-C51
BZV55-C43	BZV60-B30	BZV60-C11	BZV60-C56
BZV55-C47	BZV60-B33	BZV60-C12	BZV60-C5V1
BZV55-C4V3	BZV60-B36	BZV60-C13	BZV60-C5V6
BZV55-C4V7	BZV60-B39	BZV60-C15	BZV60-C62
BZV55-C5V1	BZV60-B3V0	BZV60-C16	BZV60-C68
BZV55-C5V6	BZV60-B3V3	BZV60-C18	BZV60-C6V2
BZV55-C6V2	BZV60-B3V6	BZV60-C20	BZV60-C6V8
BZV55-C6V8	BZV60-B3V9	BZV60-C22	BZV60-C75
BZV55-C7V5	BZV60-B43	BZV60-C24	BZV60-C7V5
BZV55-C8V2	BZV60-B47	BZV60-C27	BZV60-C8V2
BZV55-C9V1	BZV60-B4V3	BZV60-C2V4	BZV60-C9V1
BZV55-F2V4	BZV60-B4V7	BZV60-C2V7	BZV80
BZV60-B10	BZV60-B51	BZV60-C30	BZV85-C10
BZV60-B11	BZV60-B56	BZV60-C33	BZV85-C11
BZV60-B12	BZV60-B5V1	BZV60-C36	BZV85-C12
BZV60-B13	BZV60-B5V6	BZV60-C39	BZV85-C13
BZV60-B15	BZV60-B62	BZV60-C3V0	BZV85-C15
BZV60-B16	BZV60-B68	BZV60-C3V3	BZV85-C16

Multisim 14.0 Power Pro Components

BZV85-C18	BZV86-1V4	BZV90-C43	BZW03-C150
BZV85-C20	BZV86-2V0	BZV90-C47	BZW03-C16
BZV85-C22	BZV86-2V6	BZV90-C4V3	BZW03-C160
BZV85-C24	BZV86-3V2	BZV90-C4V7	BZW03-C18
BZV85-C27	BZV90-C10	BZV90-C51	BZW03-C180
BZV85-C30	BZV90-C11	BZV90-C56	BZW03-C20
BZV85-C33	BZV90-C12	BZV90-C5V1	BZW03-C200
BZV85-C36	BZV90-C13	BZV90-C5V6	BZW03-C22
BZV85-C39	BZV90-C15	BZV90-C62	BZW03-C220
BZV85-C3V6	BZV90-C16	BZV90-C68	BZW03-C24
BZV85-C3V9	BZV90-C18	BZV90-C6V2	BZW03-C240
BZV85-C43	BZV90-C20	BZV90-C6V8	BZW03-C27
BZV85-C47	BZV90-C22	BZV90-C75	BZW03-C270
BZV85-C4V3	BZV90-C24	BZV90-C7V5	BZW03-C30
BZV85-C4V7	BZV90-C27	BZV90-C8V2	BZW03-C33
BZV85-C51	BZV90-C2V4	BZV90-C9V1	BZW03-C36
BZV85-C5V1	BZV90-C2V7	BZW03-C10	BZW03-C39
BZV85-C5V6	BZV90-C30	BZW03-C100	BZW03-C43
BZV85-C62	BZV90-C33	BZW03-C11	BZW03-C47
BZV85-C68	BZV90-C36	BZW03-C110	BZW03-C51
BZV85-C6V2	BZV90-C39	BZW03-C12	BZW03-C56
BZV85-C6V8	BZV90-C3V0	BZW03-C120	BZW03-C62
BZV85-C75	BZV90-C3V3	BZW03-C13	BZW03-C68
BZV85-C7V5	BZV90-C3V6	BZW03-C130	BZW03-C75
BZV85-C8V2	BZV90-C3V9	BZW03-C15	BZW03-C7V5

Multisim 14.0 Power Pro Components

BZW03-C82	BZX384-B3V9	BZX384-C2V4	BZX55C10
BZW03-C8V2	BZX384-B43	BZX384-C2V7	BZX55C11
BZW03-C91	BZX384-B47	BZX384-C30	BZX55C12
BZW03-C9V1	BZX384-B4V3	BZX384-C33	BZX55C13
BZX100A	BZX384-B4V7	BZX384-C36	BZX55C15
BZX384-B10	BZX384-B51	BZX384-C39	BZX55C16
BZX384-B11	BZX384-B56	BZX384-C3V0	BZX55C18
BZX384-B12	BZX384-B5V1	BZX384-C3V3	BZX55C20
BZX384-B13	BZX384-B5V6	BZX384-C3V6	BZX55C22
BZX384-B15	BZX384-B62	BZX384-C3V9	BZX55C24
BZX384-B16	BZX384-B68	BZX384-C43	BZX55C27
BZX384-B18	BZX384-B6V2	BZX384-C47	BZX55C2V4
BZX384-B20	BZX384-B6V8	BZX384-C4V3	BZX55C2V7
BZX384-B22	BZX384-B75	BZX384-C4V7	BZX55C30
BZX384-B24	BZX384-B7V5	BZX384-C51	BZX55C33
BZX384-B27	BZX384-B8V2	BZX384-C56	BZX55C36
BZX384-B2V4	BZX384-B9V1	BZX384-C5V1	BZX55C39
BZX384-B2V7	BZX384-C10	BZX384-C62	BZX55C3V0
BZX384-B30	BZX384-C11	BZX384-C68	BZX55C3V3
BZX384-B33	BZX384-C12	BZX384-C6V2	BZX55C3V6
BZX384-B36	BZX384-C13	BZX384-C6V8	BZX55C3V9
BZX384-B39	BZX384-C16	BZX384-C75	BZX55C43
BZX384-B3V0	BZX384-C20	BZX384-C7V5	BZX55C47
BZX384-B3V3	BZX384-C22	BZX384-C8V2	BZX55C4V3
BZX384-B3V6	BZX384-C24	BZX384-C9V1	BZX55C4V7

Multisim 14.0 Power Pro Components

BZX55C51	BZX585-B2V4	BZX585-B9V1	BZX585-C5V1
BZX55C56	BZX585-B2V7	BZX585-C10	BZX585-C62
BZX55C5V1	BZX585-B30	BZX585-C11	BZX585-C68
BZX55C5V6	BZX585-B33	BZX585-C12	BZX585-C6V2
BZX55C62	BZX585-B36	BZX585-C13	BZX585-C6V8
BZX55C68	BZX585-B39	BZX585-C16	BZX585-C75
BZX55C6V2	BZX585-B3V0	BZX585-C20	BZX585-C7V5
BZX55C6V8	BZX585-B3V3	BZX585-C22	BZX585-C8V2
BZX55C75	BZX585-B3V6	BZX585-C24	BZX585-C9V1
BZX55C7V5	BZX585-B3V9	BZX585-C2V4	BZX79-A10
BZX55C82	BZX585-B43	BZX585-C2V7	BZX79-A11
BZX55C8V2	BZX585-B47	BZX585-C30	BZX79-A12
BZX55C91	BZX585-B4V3	BZX585-C33	BZX79-A13
BZX55C9V1	BZX585-B4V7	BZX585-C36	BZX79-A15
BZX585-B10	BZX585-B51	BZX585-C39	BZX79-A16
BZX585-B11	BZX585-B56	BZX585-C3V0	BZX79-A18
BZX585-B12	BZX585-B5V1	BZX585-C3V3	BZX79-A20
BZX585-B13	BZX585-B5V6	BZX585-C3V6	BZX79-A22
BZX585-B15	BZX585-B62	BZX585-C3V9	BZX79-A24
BZX585-B16	BZX585-B68	BZX585-C43	BZX79-A27
BZX585-B18	BZX585-B6V2	BZX585-C47	BZX79-A2V4
BZX585-B20	BZX585-B6V8	BZX585-C4V3	BZX79-A2V7
BZX585-B22	BZX585-B75	BZX585-C4V7	BZX79-A30
BZX585-B24	BZX585-B7V5	BZX585-C51	BZX79-A33
BZX585-B27	BZX585-B8V2	BZX585-C56	BZX79-A36

Multisim 14.0 Power Pro Components

BZX79-A3V0	BZX79-B15	BZX79-B6V2	BZX79-C2V4
BZX79-A3V3	BZX79-B16	BZX79-B6V8	BZX79-C2V7
BZX79-A3V6	BZX79-B18	BZX79-B75	BZX79-C30
BZX79-A3V9	BZX79-B20	BZX79-B7V5	BZX79-C33
BZX79-A40	BZX79-B22	BZX79-B8V2	BZX79-C36
BZX79-A43	BZX79-B24	BZX79-B9V1	BZX79-C39
BZX79-A47	BZX79-B27	BZX79-C10	BZX79-C3V0
BZX79-A4V3	BZX79-B2V4	BZX79-C100	BZX79-C3V3
BZX79-A4V7	BZX79-B2V7	BZX79-C11	BZX79-C3V6
BZX79-A51	BZX79-B30	BZX79-C110	BZX79-C3V9
BZX79-A56	BZX79-B33	BZX79-C12	BZX79-C43
BZX79-A5V1	BZX79-B36	BZX79-C120	BZX79-C47
BZX79-A5V6	BZX79-B39	BZX79-C13	BZX79-C4V3
BZX79-A62	BZX79-B3V3	BZX79-C130	BZX79-C4V7
BZX79-A68	BZX79-B3V6	BZX79-C15	BZX79-C51
BZX79-A6V2	BZX79-B3V9	BZX79-C150	BZX79-C56
BZX79-A6V8	BZX79-B43	BZX79-C16	BZX79-C5V1
BZX79-A75	BZX79-B47	BZX79-C160	BZX79-C5V6
BZX79-A7V5	BZX79-B4V3	BZX79-C18	BZX79-C62
BZX79-A8V2	BZX79-B4V7	BZX79-C180	BZX79-C68
BZX79-A9V1	BZX79-B51	BZX79-C20	BZX79-C6V2
BZX79-B10	BZX79-B56	BZX79-C200	BZX79-C6V8
BZX79-B11	BZX79-B5V1	BZX79-C22	BZX79-C75
BZX79-B12	BZX79-B62	BZX79-C24	BZX79-C7V5
BZX79-B13	BZX79-B68	BZX79-C27	BZX79-C82

Multisim 14.0 Power Pro Components

BZX79-C8V2	BZX83-C6V2	BZX84-A3V9	BZX84-B20
BZX79-C91	BZX83-C6V8	BZX84-A43	BZX84-B22
BZX79-C9V1	BZX83-C7V5	BZX84-A47	BZX84-B24
BZX83-C10	BZX83-C8V2	BZX84-A4V3	BZX84-B27
BZX83-C11	BZX83-C9V1	BZX84-A4V7	BZX84-B2V4
BZX83-C12	BZX84-A10	BZX84-A51	BZX84-B2V7
BZX83-C13	BZX84-A11	BZX84-A56	BZX84-B30
BZX83-C15	BZX84-A12	BZX84-A5V1	BZX84-B33
BZX83-C16	BZX84-A13	BZX84-A5V6	BZX84-B36
BZX83-C18	BZX84-A15	BZX84-A62	BZX84-B39
BZX83-C20	BZX84-A16	BZX84-A68	BZX84-B3V0
BZX83-C22	BZX84-A18	BZX84-A6V2	BZX84-B3V3
BZX83-C24	BZX84-A20	BZX84-A6V8	BZX84-B3V6
BZX83-C27	BZX84-A22	BZX84-A75	BZX84-B3V9
BZX83-C2V7	BZX84-A24	BZX84-A7V5	BZX84-B43
BZX83-C30	BZX84-A27	BZX84-A8V2	BZX84-B47
BZX83-C33	BZX84-A2V4	BZX84-A9V1	BZX84-B4V3
BZX83-C3V0	BZX84-A2V7	BZX84-B10	BZX84-B4V7
BZX83-C3V3	BZX84-A30	BZX84-B11	BZX84B4V7LT1G
BZX83-C3V6	BZX84-A33	BZX84-B12	BZX84-B51
BZX83-C3V9	BZX84-A36	BZX84-B13	BZX84-B56
BZX83-C4V3	BZX84-A39	BZX84-B15	BZX84-B5V1
BZX83-C4V7	BZX84-A3V0	BZX84-B16	BZX84B5V1LT1G
BZX83-C5V1	BZX84-A3V3	BZX84B16LT1G	BZX84-B5V6
BZX83-C5V6	BZX84-A3V6	BZX84-B18	BZX84B5V6LT1G

Multisim 14.0 Power Pro Components

BZX84-B62	BZX84-C22	BZX84-C5V1	BZX84J-B11
BZX84-B68	BZX84-C24	BZX84C5V1LT1G	BZX84J-B12
BZX84-B6V2	BZX84-C27	BZX84C5V1LT3G	BZX84J-B13
BZX84B6V2LT1G	BZX84-C2V4	BZX84-C5V6	BZX84J-B15
BZX84-B6V8	BZX84-C2V7	BZX84C5V6LT1G	BZX84J-B16
BZX84B6V8LT1G	BZX84-C30	BZX84C5V6LT3G	BZX84J-B18
BZX84-B75	BZX84-C33	BZX84-C62	BZX84J-B20
BZX84-B7V5	BZX84C33LT1G	BZX84-C68	BZX84J-B22
BZX84B7V5LT1G	BZX84C33LT3G	BZX84C68LT1G	BZX84J-B24
BZX84-B8V2	BZX84-C36	BZX84-C6V2	BZX84J-B27
BZX84B8V2LT1G	BZX84C36LT1G	BZX84C6V2LT1G	BZX84J-B2V4
BZX84-B9V1	BZX84-C39	BZX84C6V2LT3G	BZX84J-B2V7
BZX84B9V1LT1G	BZX84-C3V0	BZX84-C6V8	BZX84J-B30
BZX84-C10	BZX84C3V0LT1G	BZX84C6V8LT1G	BZX84J-B33
BZX84-C11	BZX84-C3V3	BZX84C6V8LT3G	BZX84J-B36
BZX84-C12	BZX84-C3V6	BZX84-C75	BZX84J-B39
BZX84C12LT1G	BZX84-C3V9	BZX84C75LT1G	BZX84J-B3V0
BZX84-C13	BZX84-C43	BZX84-C7V5	BZX84J-B3V3
BZX84-C15	BZX84-C47	BZX84C7V5LT1G	BZX84J-B3V6
BZX84C15LT1	BZX84-C4V3	BZX84-C8V2	BZX84J-B3V9
BZX84C15LT1G	BZX84-C4V7	BZX84C8V2LT1G	BZX84J-B43
BZX84C15LT3G	BZX84C4V7LT1G	BZX84-C9V1	BZX84J-B47
BZX84-C16	BZX84C4V7LT3G	BZX84C9V1LT1G	BZX84J-B4V3
BZX84-C18	BZX84-C51	BZX84C9V1LT3G	BZX84J-B4V7
BZX84-C20	BZX84-C56	BZX84J-B10	BZX84J-B51

Multisim 14.0 Power Pro Components

BZX84J-B56	BZX84J-C33	BZX85-C11	BZX85-C62
BZX84J-B5V1	BZX84J-C36	BZX85-C12	BZX85-C68
BZX84J-B5V6	BZX84J-C39	BZX85-C13	BZX85-C6V2
BZX84J-B62	BZX84J-C3V0	BZX85-C15	BZX85-C6V8
BZX84J-B68	BZX84J-C3V3	BZX85-C16	BZX85-C75
BZX84J-B6V2	BZX84J-C3V6	BZX85-C18	BZX85-C7V5
BZX84J-B6V8	BZX84J-C3V9	BZX85-C20	BZX85-C82
BZX84J-B75	BZX84J-C43	BZX85-C22	BZX85-C8V2
BZX84J-B7V5	BZX84J-C47	BZX85-C24	BZX85-C91
BZX84J-B8V2	BZX84J-C4V3	BZX85-C27	BZX85-C9V1
BZX84J-B9V1	BZX84J-C4V7	BZX85-C30	BZX884-B10
BZX84J-C10	BZX84J-C51	BZX85-C33	BZX884-B11
BZX84J-C11	BZX84J-C56	BZX85-C36	BZX884-B12
BZX84J-C12	BZX84J-C5V1	BZX85-C39	BZX884-B13
BZX84J-C13	BZX84J-C5V6	BZX85-C3V3	BZX884-B15
BZX84J-C15	BZX84J-C62	BZX85-C3V6	BZX884-B16
BZX84J-C16	BZX84J-C68	BZX85-C3V9	BZX884-B18
BZX84J-C18	BZX84J-C6V2	BZX85-C43	BZX884-B20
BZX84J-C20	BZX84J-C6V8	BZX85-C47	BZX884-B22
BZX84J-C22	BZX84J-C75	BZX85-C4V3	BZX884-B24
BZX84J-C24	BZX84J-C7V5	BZX85-C4V7	BZX884-B27
BZX84J-C27	BZX84J-C8V2	BZX85-C51	BZX884-B2V4
BZX84J-C2V4	BZX84J-C9V1	BZX85-C56	BZX884-B2V7
BZX84J-C2V7	BZX85-C10	BZX85-C5V1	BZX884-B30
BZX84J-C30	BZX85-C100	BZX85-C5V6	BZX884-B33

Multisim 14.0 Power Pro Components

BZX884-B36	BZX884-C13	BZX884-C7V5	CA0258E
BZX884-B39	BZX884-C16	BZX884-C8V2	CA0258M
BZX884-B3V0	BZX884-C20	BZX884-C9V1	CA0258T
BZX884-B3V3	BZX884-C22	C232A	CA0324E
BZX884-B3V6	BZX884-C24	C232B	CA0324M
BZX884-B3V9	BZX884-C2V4	C232D	CA0358AE
BZX884-B43	BZX884-C2V7	C232F	CA0358AM
BZX884-B47	BZX884-C30	C232M	CA0358AT
BZX884-B4V3	BZX884-C33	C233A	CA0358E
BZX884-B4V7	BZX884-C36	C233B	CA0358M
BZX884-B51	BZX884-C3V0	C233D	CA0358T
BZX884-B56	BZX884-C3V3	C233F	CA0741E
BZX884-B5V1	BZX884-C3V6	C233M	CA0741T
BZX884-B5V6	BZX884-C3V9	CA0124E	CA1458E
BZX884-B62	BZX884-C43	CA0124M	CA1458T
BZX884-B68	BZX884-C47	CA0158AE	CA2902M
BZX884-B6V2	BZX884-C4V3	CA0158AT	CA2902N
BZX884-B6V8	BZX884-C4V7	CA0158E	CA2904E
BZX884-B75	BZX884-C51	CA0158M	CA2904M
BZX884-B7V5	BZX884-C56	CA0158T	CA3060E
BZX884-B8V2	BZX884-C5V1	CA0224E	CA3078AE
BZX884-B9V1	BZX884-C62	CA0224M	CA3078AM
BZX884-C10	BZX884-C68	CA0258AE	CA3078AT
BZX884-C11	BZX884-C6V2	CA0258AM	CA3078E
BZX884-C12	BZX884-C75	CA0258AT	CA3078M

Multisim 14.0 Power Pro Components

CA3078T	CA3160E	CA5260AM	CLC200A8C
CA3080	CA3160T	CA5260E	CLC200AI
CA3080A	CA3193AE	CA5260M	CLC200AK
CA3080AE	CA3193AT	CA5420E	CLC200AM
CA3080AM	CA3193E	CA5420M	CLC201
CA3080E	CA3193T	CA5420T	CLC203
CA3080M	CA3240AE	CA5470E	CLC220
CA3094AE	CA3240AE1	CA5470M	CLC400A8B
CA3094AM	CA3240E	CAP_ELECTROLIT_V IRTUAL	CLC400A8D
CA3094AT	CA3240E1		CLC400AIB
CA3094BE	CA3260E	CAPACITOR_POL_R ATED	CLC400AID
CA3094BM	CA3260T	CAPACITOR_RATED	CLC400AJE
CA3094BT	CA3280E	CAPACITOR_VIRTU AL	CLC400AJP
CA3094E	CA3440AE		CLC401A8B
CA3094M	CA3440M	CCM-DCM1	CLC401A8D
CA3094T	CA3450E	CCM-DCM2	CLC401AIB
CA3100E	CA5130AE	CD4538BCM	CLC401AID
CA3100M	CA5130AM	CD4538BCN	CLC401AJE
CA3100T	CA5130AT	CD4538BCWM	CLC401AJP
CA3130E	CA5130E	CHIRP_CURRENT	CLC402A8B
CA3130M	CA5130M	CHIRP_VOLTAGE	CLC402A8D
CA3130T	CA5130T	CLC103AI	CLC402AID
CA3140E	CA5160AE	CLC103AM	CLC402AJE
CA3140M	CA5160AM	CLC111AJE	CLC402AJP
CA3140T	CA5260AE	CLC111AJP	CLC404A8D

Multisim 14.0 Power Pro Components

CLC404AID	CLC411A8B	CLC420B8D	CLC432AJP
CLC404AJE	CLC411AJE	CLC420BIB	CLC440A8B
CLC404AJM5	CLC411AJP	CLC420BJE	CLC440AJE
CLC404AJP	CLC412A8B	CLC420BJP	CLC440AJP
CLC405A8B	CLC412AIB	CLC423AJE	CLC449A8B
CLC405AIB	CLC412AJE	CLC423AJP	CLC449AJE
CLC405AJE	CLC412AJP	CLC425A8B	CLC449AJP
CLC405AJP	CLC414A8B	CLC425AIB	CLC501A8D
CLC406A8B	CLC414A8D	CLC425AJE	CLC501AID
CLC406A8D	CLC414AJE	CLC425AJP	CLC501AJE
CLC406AJE	CLC414AJP	CLC426A8B	CLC501AJP
CLC406AJM5	CLC415A8B	CLC426AIB	CLC502A8D
CLC406AJP	CLC415A8D	CLC426AJE	CLC502AID
CLC407AIB	CLC415AJE	CLC426AJP	CLC502AJE
CLC407AJE	CLC415AJP	CLC428A8B	CLC502AJP
CLC407AJP	CLC416AJE	CLC428AJE	CLC505A8D
CLC409A8D	CLC416AJP	CLC428AJP	CLC505AJE
CLC409AID	CLC417AJE	CLC430A8B	CLC505AJP
CLC409AJE	CLC417AJP	CLC430AJE	CLOCK_CURRENT
CLC409AJM5	CLC420A8B	CLC430AJP	CLOCK_VOLTAGE
CLC409AJP	CLC420A8D	CLC431A8B	CM1213A-02SR
CLC410A8B	CLC420AIB	CLC431AJE	CM1624-08DE
CLC410A8D	CLC420AJE	CLC431AJP	CNTR_16SBIN
CLC410AJE	CLC420AJP	CLC432A8B	CNTR_4ABIN
CLC410AJP	CLC420B8B	CLC432AJE	CNTR_4ADEC

Multisim 14.0 Power Pro Components

CNTR_4BIN_AS	CNY17F-3X017	COP87L40CJN	CPH5506-TL-E
CNTR_4BIN_ASCLR	CNY17F-3X019	COP87L40RJN	CPH6223-TL-E
CNTR_4BIN_S	CNY75A	COP87L42CJN	CPH6341-TL-E
CNTR_4BIN_SU_D	CNY75B	COP87L42RJN	CPH6445-TL-E
CNTR_4BINS_DC	CNY75C	CORELESS_COIL_VIRTUAL	CPH6531-TL-E
CNTR_4SBIN	COMP_4	CORESAT	CPM
CNTR_4SDEC	COMPARATOR_IDEAL	COUNT_OFF	CPV363MF
CNTR_7BIN	COMPARATOR_VIRTUAL	COUNT_OFF_HOLD	CPV364MF
CNTR_8SBIN	COMPARHYS	COUNT_OFF_RESET	CR10C12
CNTR_BCD_S	CONTROL_1A	COUNT_ON	CR10C16
CNTR_BCD_SDC	CONTROL_1C	COUNT_ON_HOLD	CR10C8
CNTR_BCD_SU_D	CONTROL_2A	COUNT_ON_RESET	CR10CY12
CNTR_BIN_DEC_SU_D	CONTROL_2C	COUNT_UPDOWN_OFF	CR10CY8
CNTR_JOHNSON	CONTROL_3A	COUNT_UPDOWN_ON	CR20F20
CNY17-1	CONTROL_3C	COUPLED_INDUCTORS	CR20F24
CNY17-2	CONTROL_4A	CPH3105-TL-E	CR6PM12
CNY17-3	CONTROL_4C	CPH3123-TL-E	CR6PM8
CNY17-4	CONTROL_NC	CPH3144-TL-E	CR8PM12
CNY17F-3	CONTROLLED_ONE_SHOT	CPH3205-TL-E	CR8PM8
CNY17F-3X001	CONVEYOR_BELT	CPH3223-TL-E	CRYSTAL_VIRTUAL
CNY17F-3X006	COP87L20CJN	CPH3448-TL-H	CS494001-LQFP(144)
CNY17F-3X007T	COP87L22CJN	CPH5505-TL-E	CS494501-TQFP(100)
CNY17F-3X009T			
CNY17F-3X016			

Multisim 14.0 Power Pro Components

CURRENT_CONTROLLED_CURRENT_SOURCE	D_FF_NEGSR	D43C6	D45H8
	D_FF_POSSR	D43C7	D45H8G
CURRENT_CONTROLLED_SPST	D_LATCH	D43C8	D45VH10G
	D_LATCH_NEGSR	D43C9	DAC7642_FP32
CURRENT_CONTROLLED_SPST_ANIMATED	D1N4148	D44C12G	DAC7643_FP32
	D42C1	D44C2	DAC8541
CURRENT_CONTROLLED_VOLTAGE_SOURCE	D42C10	D44C3	DAN222M3T5G
	D42C11	D44C5	DAP222M3T5G
CURRENT_LIMITER_BLOCK	D42C12	D44C6	DBREAK
	D42C2	D44C8	DC_CURRENT
CY37032P44-125AC	D42C3	D44H1	DC_INTERACTIVE_CURRENT
CY37032P44-125AI	D42C4	D44H10	
CY37032P44-125JC	D42C5	D44H11	DC_INTERACTIVE_VOLTAGE
CY37032P44-125JI	D42C6	D44H11G	
CY37032P44-154AC	D42C7	D44H2	DC_MACHINE_PERMANENT_MAGNET
CY37032P44-154AI	D42C8	D44H4	DC_MACHINE_WOUND_FIELD
CY37032P44-154JC	D42C9	D44H5	
CY37032P44-154JI	D43C1	D44H7	DC_POWER
CY37032P44-200AC	D43C10	D44H8	DC_XFMR
CY37032P44-200JC	D43C11	D44H8G	DCC010-TB-E
CY37032P44-222AC	D43C12	D44VH10G	DCD_2TO4
CY37032P44-222JC	D43C2	D45C12G	DCD_3TO8
CYPRESS-ULTRA-ISR-HDR	D43C3	D45H10	DCD_4TO16
	D43C4	D45H11	DCD_7SEG
D_FF	D43C5	D45H11G	DCD_7SEG_P

Multisim 14.0 Power Pro Components

DCD_BARGRAPH	DF3A6.8FUT1G	DIGITAL_HIGH	DIPSW3
DCD_HEX	DF6A6.8FUT1G	DIGITAL_LOW	DIPSW4
DCD_HEX_BLUE	DG211BDJ	DIGITAL_PULLDOWN	DIPSW5
DCD_HEX_DIG_BLUE	DG212BDJ	DIGITAL_PULLUP	DIPSW6
DCD_HEX_DIG_GREEN	DG300AAA/883	DIGITAL_STATE_MACHINE	DIPSW7
DCD_HEX_DIG_ORANGE	DG300AAK	DIODE	DIPSW8
DCD_HEX_DIG_ORANGE	DG300ACJ	DIODE	DIPSW9
DCD_HEX_DIG_RED	DG301AAA	DIODE	DIV
DCD_HEX_DIG_YELLOW	DG301AAK	DIODE_RATED	DIVIDER
DCD_HEX_GREEN	DG301ACJ	DIODE_THERMAL	DP8421A
DCD_HEX_ORANGE	DG302AAK	DIP10	DP8421A_LCC68
DCD_HEX_ORANGE	DG302ACJ	DIP12	DP8422A_LCC84
DCD_HEX_YELLOW	DG303AAK	DIP14	DPDT_DB
DEC_BCD_10_INV	DG303ACJ	DIP16	DPDT_SB
DEC_BCD_7	DG303ACY	DIP18	DPST_2NC_DB
DEC2_4	DG304ACJ	DIP20	DPST_2NC_SB
DEC3_8	DG308BDJ	DIP22	DPST_2NO_DB
DEC4_10	DG309BDJ	DIP24	DPST_2NO_SB
DELAY	DG381ACJ	DIP28	DQ_TO_ABC
DEM4_16	DG411DY	DIP4	DRA5B
DF06MA-E3/45	DGND	DIP6	DRA5C
DF10S/45	DIGITAL_CLOCK	DIP8	DRA5E
DF10SA-E3/45	DIGITAL_CONSTANT	DIPSW1	DRA5G
DF1510S-E3/77	DIGITAL_FREQUENCY_DIVIDER	DIPSW10	DRA8B
		DIPSW2	DRA8C

Multisim 14.0 Power Pro Components

DRA8E	DS80C323_LCC44	DSWPK_4	DTA143EM3T5G
DRA8G	DS83C520_LCC44	DSWPK_5	DTA143ZET1G
DRV103H	DS83C530_FP52	DSWPK_6	DTA143ZM3T5G
DRV103U	DS87C520_LCC44	DSWPK_7	DTA144EET1G
DRV104PWP	DS87C530_FP52	DSWPK_8	DTA144EM3T5G
DRV1100P	DSP16210- TQFP(144)	DSWPK_9	DTA144TET1G
DRV1100U		DTA113EET1G	DTA144TM3T5G
DRV134PA	DSP1628- BQFP(100)	DTA113EM3T5G	DTA144WM3T5G
DRV134UA	DSP1628- TQFP(100)	DTA114EET1G	DTAND
DRV135UA		DTA114EM3T5G	DTC113EET1G
DRV8832DGQ	DSP16410B- PBGA(208)	DTA114TET1G	DTC113EM3T5G
DRV8832DRCR	DSUB15F	DTA114TM3T5G	DTC114EET1G
DS1846_SO20	DSUB15F-VGA	DTA114YET1G	DTC114EM3T5G
DS26C32AME	DSUB15M	DTA114YM3T5G	DTC114TET1G
DS26C32ATN	DSUB15M-VGA	DTA115EET1G	DTC114TM3T5G
DS3486J	DSUB25F	DTA115EM3T5G	DTC114YET1G
DS3486M	DSUB25M	DTA115TET1G	DTC115EET1G
DS3486N	DSUB37F	DTA115TM3T5G	DTC115EM3T5G
DS34C86TM	DSUB37M	DTA123EM3T5G	DTC115TET1G
DS34C86TN	DSUB9F	DTA123TET1G	DTC115TM3T5G
DS34F86J	DSUB9M	DTA123TM3T5G	DTC123EM3T5G
DS35F86J	DSWPK_10	DTA124EET1G	DTC123JET1G
DS75129N	DSWPK_2	DTA124EM3T5G	DTC123JM3T5G
DS80C310_LCC44	DSWPK_3	DTA124XM3T5G	DTC123TET1G
DS80C320_LCC44		DTA143EET1G	DTC123TM3T5G

Multisim 14.0 Power Pro Components

DTC124EET1G	ECH8654-TL-H	EGP50G-E3/54	EL4089CN
DTC124EM3T5G	ECH8657-TL-H	EL2006CG	EL4089CS
DTC124XET1G	ECH8660-TL-H	EL2006G	EL4430CN
DTC124XM3T5G	ECH8662-TL-H	EL2006G/883B	EL4430CS
DTC143EET1G	EDF1DS-E3/45	EL2022/EL	EL4451CN
DTC143EM3T5G	EDR201A05	EL2022CG	EL4451CS
DTC143TM3T5G	EDR201A12	EL2022G	EL4452CN
DTC143ZET1G	EDR201A24	EL2157CN	EL4452CS
DTC143ZM3T5G	EDR2H1A05	EL2157CS	ELH0032G/883B
DTC144EET1G	EDR2H1A12	EL2210CN	ELH0101K/883B
DTC144EM3T5G	EDR2H1A24	EL2210CS	EMC2DXV5T1G
DTC144TET1G	EGF1D-E3/67A	EL2211CN	EMC3DXV5T1G
DTC144TM3T5G	EGF1T-E3/67A	EL2211CS	EMC3DXV5T5G
DTC144WM3T5G	EGG06_02	EL2310CN	EMC4DXV5T1G
DTMF_KEYPAD	EGG06_04	EL2310CS	EMC5DXV5T1G
ECG6407	EGG06_06	EL2311CN	EMH1303-TL-E
ECG6408	EGG06_08	EL2311CS	EMH1405-TL-H
ECG6411	EGH16_06	EL2410CN	EMR011A03
ECG6412	EGH16_08	EL2410CS	EMR011A05
ECH8102-TL-H	EGH16_10	EL2411CN	EMR011A06
ECH8649-TL-H	EGH16_12	EL2411CS	EMR011A08
ECH8651R-R-TL-H	EGH16_16	EL2500/EL	EMR011A09
ECH8651R-TL-H	EGP10D-E3/54	EL2520/EL	EMR011A12
ECH8652-TL-H	EGP10G-E3/54	EL2600/EL	EMR011A24
ECH8653-TL-H	EGP50D-E3/54	EL2620/EL	EMR011B03

Multisim 14.0 Power Pro Components

EMR011B05	EMR031A12	EMR131A06	EMR171A03
EMR011B06	EMR031A24	EMR131A08	EMR171A05
EMR011B08	EMR031B03	EMR131A09	EMR171A06
EMR011B09	EMR031B05	EMR131A12	EMR171A08
EMR011B12	EMR031B06	EMR131A24	EMR171A09
EMR011B24	EMR031B08	EMR131B03	EMR171A12
EMR021A03	EMR031B09	EMR131B05	EMR171A24
EMR021A05	EMR031B12	EMR131B06	EMX1DXV6T1G
EMR021A06	EMR031B24	EMR131B08	EMX1DXV6T5G
EMR021A08	EMR121A03	EMR131B09	EN2016CM
EMR021A09	EMR121A05	EMR131B12	EN2016CN
EMR021A12	EMR121A06	EMR131B24	ENC_10TO4
EMR021A24	EMR121A08	EMR151A03	ENC_8TO3
EMR021B03	EMR121A09	EMR151A05	ENC_8TO3S
EMR021B05	EMR121A12	EMR151A06	ENC10_4
EMR021B06	EMR121A24	EMR151A08	ENC8_3
EMR021B08	EMR121B03	EMR151A09	ENERGIZING_COIL
EMR021B09	EMR121B05	EMR151A12	ENERGIZING_COIL_ AC
EMR021B12	EMR121B06	EMR151A24	ENERGIZING_COIL_ TIMED
EMR021B24	EMR121B08	EMR161A03	
EMR031A03	EMR121B09	EMR161A05	EP2015ACN
EMR031A05	EMR121B12	EMR161A06	EP2015CM
EMR031A06	EMR121B24	EMR161A08	EP2015CN
EMR031A08	EMR131A03	EMR161A09	EPC2001
EMR031A09	EMR131A05	EMR161A12	EPC2007

Multisim 14.0 Power Pro Components

EPC2010	EPM7032-PLCC(44)	EPM7128AE-TQFP(144)	ESD5B5.0ST1G
EPC2012	EPM7032-PQFP(44)		ESD5V3L1B-02LS
EPC2014	EPM7032S-PLCC(44)	EPM7128A-PLCC(84)	ESD5V3U4U-HDMI
EPC2015		EPM7128A-TQFP(100)	ESD5Z12T1G
EPC2016	EPM7032S-TQFP(44)		ESD5Z2.5T1G
EPC2018	EPM7032-TQFP(44)	EPM7128A-TQFP(144)	ESD5Z3.3T1G
EPC2019	EPM7064-PLCC(44)		ESD5Z5.0T1G
EPC2020	EPM7064-PLCC(68)	EPM7512AE-PQFP(208)	ESD5Z6.0T1G
EPC2021	EPM7064-PLCC(84)	EPM7512AE-TQFP(144)	ESD5Z7.0T1G
EPC2022	EPM7064-PQFP(100)		ESD5Z7.0T5G
EPC2023		ERRAMP	ESD7004MUTAG
EPC2024	EPM7064S-PLCC(44)	ES1B-E3/61T	ESD7008MUTAG
EPC2025		ES1C-E3/61T	ESD7016MUTAG
EPC2100	EPM7064S-PLCC(84)	ES1D-E3/61T	ESD7104MUTAG
EPC2801	EPM7064S-TQFP(100)	ES1PD-E3/84A	ESD7951ST5G
EPC2815		ES2B-E3/52T	ESD7C3.3DT5G
EPC2818	EPM7064S-TQFP(44)	ES2C-E3/52T	ESD7C5.0DT5G
EPC8002	EPM7064-TQFP(44)	ES2D-E3/52T	ESD8004MUTAG
EPC8003	EPM7096-PLCC(68)	ES3D-E3/57T	ESD8040MUTAG
EPC8004	EPM7096-PLCC(84)	ESD0P2RF-02LRH	ESD8V0R1B-02EL
EPC8005		ESD0P2RF-02LS	ESD8V0R1B-02ELS
EPC8007	EPM7096-PQFP(100)	ESD11L5.0DT5G	ESD9B3.3ST5G
EPC8008	EPM7128AE-PLCC(84)	ESD18VU1B-02LRH	ESD9B5.0ST5G
EPC8009		ESD18VU1B-02LS	ESD9C3.3ST5G
EPC8010	EPM7128AE-TQFP(100)	ESD3V3U4ULC	ESD9C5.0ST5G

Multisim 14.0 Power Pro Components

ESD9L5.0ST5G	F1072	FCX749	FM_VOLTAGE
ESD9X12ST5G	F1074	FEP16DT-E3/45	FMMD2835
ESD9X3.3ST5G	F1120	FEP30GP-E3/45	FMMD2836
ESD9X5.0ST5G	F1174	FEP30JPE3/45	FMMD2837
ESDR0502NMUTAG	F1214	FES16BT-E3/45	FMMD2838
ESDR0502NMUTBG	F1240	FES16GT-E3/45	FMMD6050
ESDR0544MDMR4G	F1260	FES8DT-E3/45	FMMD6100
ESH1PD-E3/84A	F2001	FF_D_CO	FMMD7000
ET382	F2002	FF_D_PCLR_CO	FMMD914
ET386	F2012	FF_D4_CLR_CO	FMMT38B
ET393	F2021	FF_JK_NSCLR_CO	FMMT489
EVAL-SDP-CB1Z	F2046	FF_JK_PSCLR_CO	FMMT491A
EVAL-SDP-CH1Z	F2047	FF_T_CLR_CO	FMMT497
EVAL-SDP-CH1Z_FMC	F2048	FF200R12KE4	FMMT5179
EVAL-SDP-CS1Z	F2201S	FF300R12KE4	FMMT549
	F2202S	FF450R12KE4	FMMT589
EXPONENTIAL_CURRENT	FAST_1A	FLOAT_NC	FMMT591A
EXPONENTIAL_VOLTAGE	FAST_2A	FLOAT_NO	FMMT597
	FAST_3A	FLOW_NC	FMMT597Q
F1007	FAST_4A	FLOW_NO	FMMT617
F1008	FCN-268D024-G/10-R	FLYBACKCCM	FMMT618
F1020		FLYBACKCM	FMMT619
F1021	FCX458	FLYBACKDCM	FMMT624
F1022	FCX558	FLYBACKVM	FMMT625
F1027	FCX649	FM_CURRENT	FMMT717

Multisim 14.0 Power Pro Components

FMMT718	FREQUENCY_TABLE	FZT1053A	FZT789A
FMMT720	_FUNCTION	FZT1147A	FZT790A
FMMT722	FS100R12KT4	FZT1149A	FZT792A
FMMT723	FS150R12KT4	FZT1151A	FZT795A
FMMT918	FS25R12W1T4	FZT604	FZT796A
FMMTA20	FS50R12W2T4	FZT605	FZT849
FMMTA70	FS75R12W2T4	FZT649	FZT851
FMMTH10	FSK_VOLTAGE	FZT651	FZT857
FMMV105G	FULL_ADDER	FZT653	FZT869
FMMV109	FULL_CM	FZT657	FZT948
FMMV2101	FULL_VM	FZT658	FZT949
FMMV2102	FUSE	FZT688B	FZT951
FMMV2103	FUSE_RATED	FZT689B	FZT953
FMMV2104	FUSE_VIRTUAL	FZT690B	FZT955
FMMV2105	FWDCCM	FZT692B	FZT956
FMMV2106	FWDDCM	FZT694B	FZT957
FMMV2107	FX2-100S- 1.27DS(71)	FZT696B	FZT958
FMMV2108	FX8-120P-SV1(91)	FZT705	FZT968
FMMV2109	FX8-120S-SV(21)	FZT749	G3SBA60-E3/51
FMMV3102	FZ600R12KE4	FZT751	GaAsFET_N
FOOT_NC	FZ900R12KP4	FZT753	GaAsFET_P
FOOT_NO	FZT1047A	FZT757	GAIN_2_PIN
FORWARDCM	FZT1048A	FZT758	GBPC3506W-E4/51
FORWARDVM	FZT1049A	FZT788A	GBU4G-E3/45
FREQ_DIVIDER	FZT1051A	FZT788B	GBU4M-E3/51

Multisim 14.0 Power Pro Components

GBU6G-E3/45	GL34B	GLL4755	GP10M
GBU6M-E3/45	GL34D	GLL4756	GP10N
GEARS	GL34G	GLL4757	GP10Q
GEN_CNTR_4ABIN	GL34G-E3/98	GLL4758	GP10T
GF1A	GL34J	GLL4759	GP10V
GF1B	GLL4735	GLL4760	GP10W
GF1D	GLL4736	GLL4761	GP10Y
GF1G	GLL4737	GLL4762	GP10Y-E3/54
GF1G-E3/67A	GLL4738	GLL4763	GP15A
GF1J	GLL4739	GP02-20	GP15B
GF1K	GLL4740	GP02-25	GP15D
GF1M	GLL4741	GP02-30	GP15G
GI250-1	GLL4742	GP02-35	GP15J
GI250-2	GLL4743	GP02-40	GP15K
GI250-3	GLL4744	GP08A	GP15M
GI250-4	GLL4745	GP08B	GP20A
GI751-E3/54	GLL4746	GP08D	GP20B
GI810	GLL4747	GP08G	GP20D
GI811	GLL4748	GP08J	GP20G
GI812	GLL4749	GP10A	GP20J
GI814	GLL4750	GP10B	GP30A
GI816	GLL4751	GP10D	GP30B
GI817	GLL4752	GP10G	GP30D
GI818	GLL4753	GP10J	GP30G
GL34A	GLL4754	GP10K	GP30J

Multisim 14.0 Power Pro Components

GP30K	H11AV3	HA1-5104-5	HA2-2512-2
GP30M	H11AV3A	HA1-5114-2	HA2-2515-2
GRAPH_LCD_L	H11B1	HA1-5114-5	HA2-2520-2
GRAPH_LCD_M	H11B2	HA1-5134-2	HA2-2522-2
GRAPH_LCD_S	H11B3	HA1-5134-5	HA2-2525-5
GROUND	H11D1	HA1-5190-2	HA2-2529-2
GROUND_REF1	H11D2	HA17339	HA2-2529-5
GROUND_REF2	H11D3	HA17339F	HA2-2541-2
GROUND_REF3	H11D4	HA17393	HA2-2541-5
GROUND_REF4	HA1-2539-2	HA17393F	HA2-2542-2
GROUND_REF5	HA1-2539-5	HA17901FP	HA2-2542-5
GSB311A41EU	HA1-2540-2	HA17901FPJ	HA2-2544-2
GSB3211311WEU	HA1-2540-5	HA17901FPK	HA2-2548-5
GSIB1580-E3/45	HA1-2541-2	HA17901G	HA2-2548-9
GSIB2560-E3/45	HA1-2541-5	HA17901P	HA2-2600-2
GTO	HA1-2542-2	HA17901PJ	HA2-2602-2
H11A1	HA1-2542-5	HA17903FP	HA2-2605-5
H11A2	HA1-2839-5	HA17903FPJ	HA2-2620-2
H11A3	HA1-2840-5	HA17903FPK	HA2-2622-2
H11A4	HA1-2840-9	HA17903GS	HA2-2625-5
H11A5	HA1-2850-5	HA17903PS	HA2-2640-2
H11AV1	HA1-2850-9	HA17903PSJ	HA2-5101-2
H11AV1A	HA1-4741-2	HA2-2500-2	HA2-5102-2
H11AV2	HA1-4741-5	HA2-2502-2	HA2-5102-5
H11AV2A	HA1-5104-2	HA2-2510-2	HA2-5130-5

Multisim 14.0 Power Pro Components

HA2-5135-5	HA3-2544C-5	HA3-5177-5	HA7-2529-5
HA2-5142-2	HA3-2548-5	HA3-5221-5	HA7-2544-2
HA2-5142-5	HA3-2605-5	HA3-5222-5	HA7-2544-5
HA2-5147-2	HA3-2625-5	HA3-5232-5	HA7-2548-5
HA2-5147-5	HA3-2839-5	HA3-5232-9	HA7-2600-2
HA2-5160-2	HA3-2839-9	HA3-7712A-5	HA7-2602-2
HA2-5160-5	HA3-2840-5	HA3-7712A-9	HA7-2605-5
HA2-5162-5	HA3-2840-9	HA3-7712B-5	HA7-2620-2
HA2-5170-2	HA3-2841-5	HA3-7712B-9	HA7-2622-2
HA2-5170-5	HA3-2841-9	HA3B2840-5	HA7-2625-5
HA2-5190-2	HA3-2842-5	HA3B2840-9	HA7-2640-2
HA2-5221-5	HA3-2842-9	HA3B2841-5	HA7-2645-5
HA2-7712A-5	HA3-2850-5	HA3B2841-9	HA7-2840-5
HA2-7712A-9	HA3-2850-9	HA3B2842-5	HA7-2840-9
HA2-7712B-5	HA3-4741-5	HA3B2842-9	HA7-2850-5
HA2-7712B-9	HA3-5101-5	HA3B2850-5	HA7-2850-9
HA3-2444-5	HA3-5102-5	HA3B2850-9	HA7-5101-2
HA3-2444-9	HA3-5104-5	HA4P2525-5	HA7-5102-2
HA3-2525-5	HA3-5111-5	HA7-2500-2	HA7-5102-5
HA3-2529-5	HA3-5112-5	HA7-2510-2	HA7-5111-2
HA3-2539-5	HA3-5114-5	HA7-2512-2	HA7-5112-2
HA3-2539C-5	HA3-5127-5	HA7-2515-2	HA7-5127-2
HA3-2540-5	HA3-5127A-5	HA7-2520-2	HA7-5127-5
HA3-2542-5	HA3-5142-5	HA7-2522-2	HA7-5127A-2
HA3-2544-5	HA3-5147-5	HA7-2525-5	HA7-5127A-5

Multisim 14.0 Power Pro Components

HA7-5130-2	HA9P2544C-5	HA9P5114-9	HC-49/US_25MHz
HA7-5130-5	HA9P2544C-9	HA9P5127-5	HC-49/US_40MHz
HA7-5135-2	HA9P2548-5	HA9P5137-5	HC-49/US_5MHz
HA7-5135-5	HA9P2605-5	HA9P5142-9	HC-49/US_7MHz
HA7-5137-2	HA9P2625-5	HA9P5221-5	HCNR200
HA7-5137-5	HA9P2840-5	HA9P5222-5	HCNR200-000E
HA7-5142-2	HA9P2840-9	HA9P5222-9	HCNR200-050E
HA7-5142-5	HA9P2841-5	HA9P5232-5	HCNR200-300E
HA7-5147-2	HA9P2841-9	HA9P5232-9	HCNR200-350E
HA7-5147-5	HA9P2842-5	HA9P7712B-5	HCNR201
HA7-5170-2	HA9P2842-9	HA9P7712B-9	HCNW136-000E
HA7-5170-5	HA9P2850-5	HALF_ADDER	HCNW136-300E
HA7-5177-5	HA9P2850-9	HALF_CM	HCNW139-000E
HA7-5221-5	HA9P4741-9	HALF_VM	HCNW139-300E
HA7-5221-9	HA9P5101-5	HC-49/U_1.5MHz	HCNW2201-000E
HA7-5222-5	HA9P5101-9	HC-49/U_11MHz	HCNW2201-300E
HA7-5222-9	HA9P5102-5	HC-49/U_15MHz	HCNW3120-000E
HA9P2444-5	HA9P5102-9	HC-49/U_25MHz	HCNW3120-300E
HA9P2444-9	HA9P5104-5	HC-49/U_3MHz	HCPL-0201-000E
HA9P2529-5	HA9P5104-9	HC-49/U_40MHz	HCPL-0201-060E
HA9P2539-5	HA9P5111-5	HC-49/U_5MHz	HCPL-0211-000E
HA9P2539-9	HA9P5111-9	HC-49/U_7MHz	HCPL-0211-060E
HA9P2540-5	HA9P5112-5	HC-49/U_80MHz	HCPL-0302-000E
HA9P2544-5	HA9P5112-9	HC-49/US_11MHz	HCPL-0302-060E
HA9P2544-9	HA9P5114-5	HC-49/US_15MHz	HCPL-0314-000E

Multisim 14.0 Power Pro Components

HCPL-0314-060E	HCPL-2211-060E	HCPL-3120-060E	HD64F2134FA20
HCPL-0454-000E	HCPL-2211-300E	HCPL-3120-300E	HD64F2134TF20
HCPL-0454-060E	HCPL-2211-360E	HCPL-3120-360E	HD64F2134VFA10
HCPL-0466-000E	HCPL-2212-000E	HCPL-3140-000E	HD64F2134VTF10
HCPL-0466-060E	HCPL-2212-060E	HCPL-3140-060E	HDR1X10
HCPL-0501-500E	HCPL-2212-300E	HCPL-3140-300E	HDR1X11
HCPL-0501-560E	HCPL-2212-360E	HCPL-3140-360E	HDR1X12
HCPL0631	HCPL-2219-000E	HCPL-316J-000E	HDR1X13
HCPL-063L-000E	HCPL-2219-060E	HCPL-4504-000E	HDR1X14
HCPL-063L-060E	HCPL-2219-300E	HCPL-4504-020E	HDR1X15
HCPL-0701-000E	HCPL-2219-360E	HCPL-4504-060E	HDR1X16
HCPL-0701-060E	HCPL-2231-000E	HCPL-4504-300E	HDR1X17
HCPL-181-000E	HCPL-2231-300E	HCPL-4504-320E	HDR1X18
HCPL-181-060E	HCPL-2232-000E	HCPL-4504-360E	HDR1X19
HCPL-2200-000E	HCPL-2232-300E	HCPL-4506-000E	HDR1X2
HCPL-2200-300E	HCPL-263L-000E	HCPL-4506-020E	HDR1X20
HCPL-2201-000E	HCPL-263L-020E	HCPL-4506-060E	HDR1X21
HCPL-2201-060E	HCPL-263L-060E	HCPL-4506-300E	HDR1X22
HCPL-2201-300E	HCPL-263L-300E	HCPL-4506-320E	HDR1X23
HCPL-2201-360E	HCPL-263L-320E	HCPL-4506-360E	HDR1X24
HCPL-2202-000E	HCPL-263L-560E	HCPL-7800-000E	HDR1X25
HCPL-2202-060E	HCPL-3020-000E	HCPL-7800-300E	HDR1X3
HCPL-2202-300E	HCPL-3020-060E	HCPL-J312-000E	HDR1X4
HCPL-2202-360E	HCPL-3020-300E	HCPL-J312-300E	HDR1X5
HCPL-2211-000E	HCPL-3120-000E	HD4A	HDR1X6

Multisim 14.0 Power Pro Components

HDR1X7	HDR2X8	HFA2-0002-9	HFB35HB20
HDR1X8	HDR2X9	HFA2-0005-5	HFB35HB20C
HDR1X9	HELD_CLOSED_LIMIT	HFA2-0005-9	HFB50HC20
HDR2X10	T	HFA25TB60	HFB50HC20C
HDR2X11	HELD_OPEN_LIMIT	HFA3-0001-5	HFB50HI20
HDR2X12	HF30ACC201209	HFA3-0001-9	HFB50HI20C
HDR2X13	HF30ACC321611	HFA3-0002-5	HFB60HF20
HDR2X14	HF30ACC322513	HFA3-0002-9	HFB60HF20C
HDR2X15	HF30ACC453215	HFA3-0005-5	HM1-65642-883
HDR2X16	HF50ACC201209	HFA3-0005-9	HM1-65642B-883
HDR2X17	HF50ACC321611	HFA30PA60C	HM1-65642C-883
HDR2X18	HF50ACC322513	HFA35HB120	HM4-65642-883
HDR2X19	HF50ACC453215	HFA45HC60C	HM4-65642B-883
HDR2X2	HF70ACC201209	HFA7-0002-5	HM6116A120
HDR2X20	HF70ACC321611	HFA7-0002-9	HMA510GM-55/833
HDR2X21	HF70ACC322513	HFA7-0005-5	
HDR2X22	HF70ACC453215	HFA7-0005-9	HMA510GM-65/833
HDR2X23	HFA04TB60	HFA9P0001-5	HMA510GM-75/833
HDR2X24	HFA08PB120	HFA9P0002-5	
HDR2X25	HFA08TB60	HFA9P0002-9	HOLDING_TANK
HDR2X3	HFA1-0001-5	HFA9P0005-5	HSDL-5400
HDR2X4	HFA1-0001-9	HFA9P0005-9	HSDL-5420
HDR2X5	HFA15TB60	HFB16HY20C	HSDL-5420#031
HDR2X6	HFA16PB120	HFB20HJ20C	HSP43124PC-33
HDR2X7	HFA2-0002-5	HFB25HJ20	HSP43124PC-45

Multisim 14.0 Power Pro Components

HSP43168GM-25/883	ICL7652P	IDD03SG60C	IDH08G65C5
	ICM7555ESA+	IDD04SG60C	IDH08S120
HSP43168GM-33/883	ICM7555IJA+	IDD05SG60C	IDH08S60C
	ICM7555IPA+	IDD06E60	IDH08SG60C
HSP45240GM-25/883	ICM7555ISA+	IDD06SG60C	IDH09G65C5
	ICM7555ITV	IDD08SG60C	IDH09SG60C
HSP45240GM-40/883	ICM7555MJA	IDD09E60	IDH10G65C5
	ICM7555MTV	IDD09SG60C	IDH10S120
ICL7611ACPA	ICM7556IPD+	IDD10SG60C	IDH10S60C
ICL7611ACTV	ICM7556ISD+	IDD12SG60C	IDH10SG60C
ICL7611AMTV	ICM7556MJD+	IDD15E60	IDH12G65C5
ICL7611DCBA	IDAC	IDD23E60	IDH12S60C
ICL7650SCBA-1	IDAC16	IDH02G65C5	IDH15S120
ICL7650SCBD	IDB04E120	IDH02SG120	IDH16G65C5
ICL7650SCPA	IDB06E60	IDH03G65C5	IDH16S60C
ICL7650SCPD	IDB09E120	IDH04G65C5	IDH20G65C5
ICL7650SCTV-1	IDB09E60	IDH04S60C	IDL02G65C5
ICL7650SIJD	IDB12E120	IDH04SG60C	IDL04G65C5
ICL7650SIPA-1	IDB15E60	IDH05G65C5	IDL06G65C5
ICL7650SIPD	IDB18E120	IDH05S120	IDL08G65C5
ICL7650SITV-1	IDB23E60	IDH05S60C	IDL10G65C5
ICL7650SMJD	IDB30E120	IDH05SG60C	IDL12G65C5
ICL7650SMTV-1	IDB30E60	IDH06G65C5	IDP04E120
ICL7652	IDB45E60	IDH06S60C	IDP06E60
ICL7652D	IDD03E60	IDH06SG60C	IDP09E120

Multisim 14.0 Power Pro Components

IDP09E60	IDT7210L55F	INA101CG	INA111BP
IDP12E120	IDT7210L55G	INA101CM	INA111BU
IDP15E60	IDT7210L55J	INA101HP	INA114AP
IDP18E120	IDT7210L65C	INA101SG	INA114AU
IDP23E60	IDT7210L65F	INA101SM	INA114BP
IDP30E120	IDT7210L65G	INA102AG	INA114BU
IDP30E60	IDT7210L65J	INA102AU	INA115AU
IDP45E60	IDW10G65C5	INA102CG	INA115BU
IDT7210L20C	IDW10S120	INA102KP	INA117AM
IDT7210L20F	IDW12G65C5	INA103KP	INA117BM
IDT7210L20G	IDW15S120	INA103KU	INA117KU
IDT7210L20J	IDW16G65C5	INA105_CMP	INA117P
IDT7210L25C	IDW20G65C5	INA105AM	INA117SM
IDT7210L25F	IDW20S120	INA105BM	INA118P
IDT7210L25G	IDW30G65C5	INA105KP	INA118PB
IDT7210L25J	IDW30S120	INA105KU	INA118U
IDT7210L35C	IDW40G65C5	INA106KP	INA118UB
IDT7210L35F	IGBT_DIODE_THER MAL	INA106U	INA120AP
IDT7210L35G	IJW120R070T1	INA110AG	INA120BG
IDT7210L35J	IJW120R100T1	INA110BG	INA120BP
IDT7210L45C	ILLUMINATED_PB	INA110KP	INA120CG
IDT7210L45F	IMSA110-G20S	INA110KU	INA121P
IDT7210L45G	INA101AG	INA110SG	INA121PA
IDT7210L45J	INA101AM	INA111AP	INA121U
IDT7210L55C		INA111AU	INA121UA

Multisim 14.0 Power Pro Components

INA122P	INA132UA	INA193AID	INA213BIDCKR
INA122PA	INA133U	INA194AID	INA213BIRSWR
INA122U	INA133UA	INA195AID	INA214AIDCKR
INA122UA	INA134PA	INA201AID	INA214AIRSWR
INA125P	INA134UA	INA201AIDGKR	INA214BIDCKR
INA125PA	INA137PA	INA206AID	INA214BIRSWR
INA125U	INA137UA	INA206AIPW	INA216A2RSWR
INA125UA	INA138NA	INA210AIDCKR	INA216A2YFFR
INA126P	INA143U	INA210AIRSWR	INA216A3RSWR
INA126PA	INA143UA	INA210BIDCKR	INA216A3YFFR
INA126U	INA145UA	INA210BIRSWR	INA216A4RSWR
INA126UA	INA146UA	INA211AIDCKR	INA216A4YFFR
INA128P	INA148UA	INA211BIDCKR	INA270AID
INA128PA	INA152EA/250	INA2126E/250	INA271AID
INA128U	INA154U	INA2126EA/250	INA321E
INA128UA	INA154UA	INA2126P	INA321EA
INA129P	INA155U	INA2126U	INA322EA
INA129PA	INA155UA	INA2128UA	INA326EA
INA129U	INA157U	INA212AIDCKR	INA327EA
INA129UA	INA157UA	INA212BIDCKR	INA331AIDGK
INA131AP	INA159AID	INA2132U	INA331IDGK
INA131BP	INA163UA	INA2132UA	INA332IDGK
INA132P	INA168NA	INA213AIDCKR	INA333AIDGKR
INA132PA	INA169NA	INA213AIDCKT	INA333AIDRGR
INA132U	INA170EA	INA213AIRSWR	

Multisim 14.0 Power Pro Components

INCREMENTAL_ENC ORDER	IPA045N10N3 G	IPA60R125C6	IPA65R190CFD
INDICATOR	IPA057N06N3 G	IPA60R125CP	IPA65R190E6
INDUCTION_MACHI NE_SQUIRREL_CAG E	IPA057N08N3 G	IPA60R160C6	IPA65R225C7
	IPA075N15N3 G	IPA60R165CP	IPA65R280C6
	IPA086N10N3 G	IPA60R190C6	IPA65R280E6
INDUCTION_MACHI NE_SQUIRREL_CAG E_E	IPA093N06N3 G	IPA60R190E6	IPA65R310CFD
	IPA100N08N3 G	IPA60R199CP	IPA65R380C6
INDUCTION_MACHI NE_WOUND	IPA105N15N3 G	IPA60R250CP	IPA65R380E6
	IPA126N10N3 G	IPA60R280C6	IPA65R420CFD
INDUCTION_MACHI NE_WOUND_E	IPA180N10N3 G	IPA60R280E6	IPA65R600C6
INDUCTOR_ADVAN CED	IPA50R140CP	IPA60R299CP	IPA65R600E6
	IPA50R190CE	IPA60R380C6	IPA65R660CFD
INDUCTOR_COUPLI NG	IPA50R199CP	IPA60R380E6	IPA90R1K0C3
Inductor_Lossy	IPA50R250CP	IPA60R385CP	IPA90R1K2C3
INDUCTOR_RATED	IPA50R280CE	IPA60R520C6	IPA90R340C3
	IPA50R299CP	IPA60R520E6	IPA90R500C3
INDUCTOR_VIRTUA L	IPA50R350CP	IPA60R600C6	IPA90R800C3
INERTIAL_LOAD	IPA50R380CE	IPA60R600E6	IPB009N03L G
INTERACTIVE_DIGIT AL_CONSTANT	IPA50R399CP	IPA60R950C6	IPB010N06N
	IPA50R500CE	IPA65R045C7	IPB011N04L G
INV	IPA50R520CP	IPA65R065C7	IPB011N04N G
IPA028N08N3 G	IPA50R650CE	IPA65R095C7	IPB014N06N
IPA030N10N3 G	IPA50R800CE	IPA65R125C7	IPB015N04L G
IPA032N06N3 G	IPA50R950CE	IPA65R190C6	IPB015N04N G
IPA037N08N3 G	IPA60R099C6	IPA65R190C7	IPB016N06L3 G

Multisim 14.0 Power Pro Components

IPB017N06N3 G	IPB041N04N G	IPB107N20NA	IPB60R250CP
IPB019N06L3 G	IPB042N03L G	IPB108N15N3 G	IPB60R385CP
IPB019N08N3 G	IPB042N10N3 G	IPB114N03L G	IPB65R045C7
IPB020N04N G	IPB048N06L G	IPB123N10N3 G	IPB65R065C7
IPB020NE7N3 G	IPB049N06L3 G	IPB136N08N3 G	IPB65R095C7
IPB021N06N3 G	IPB049NE7N3 G	IPB144N12N3 G	IPB65R110CFDA
IPB022N04L G	IPB050N06N G	IPB147N03L G	IPB65R125C7
IPB023N04N G	IPB052N04N G	IPB200N15N3 G	IPB65R150CFDA
IPB023N06N3 G	IPB054N06N3 G	IPB200N25N3 G	IPB65R190C7
IPB025N08N3 G	IPB054N08N3 G	IPB230N06L3 G	IPB65R190CFD
IPB025N10N3 G	IPB055N03L G	IPB260N06N3 G	IPB65R190CFDA
IPB026N06N	IPB057N06N	IPB26CN10N G	IPB65R225C7
IPB027N10N3 G	IPB065N03L G	IPB320N20N3 G	IPB65R310CFDA
IPB029N06N3 G	IPB065N15N3 G	IPB34CN10N G	IPB65R660CFD
IPB030N08N3 G	IPB067N08N3 G	IPB50CN10N G	IPB65R660CFDA
IPB031NE7N3 G	IPB072N15N3 G	IPB50R140CP	IPD025N06N
IPB034N03L G	IPB075N04L G	IPB50R199CP	IPD031N03L G
IPB034N06L3 G	IPB080N03L G	IPB50R250CP	IPD031N06L3 G
IPB034N06N3 G	IPB081N06L3 G	IPB50R299CP	IPD034N06N3 G
IPB035N08N3 G	IPB083N10N3 G	IPB530N15N3 G	IPD035N06L3 G
IPB036N12N3 G	IPB090N06N3 G	IPB600N25N3 G	IPD036N04L G
IPB037N06N3 G	IPB093N04L G	IPB60R099CP	IPD038N04N G
IPB038N12N3 G	IPB096N03L G	IPB60R125CP	IPD038N06N3 G
IPB039N04L G	IPB097N08N3 G	IPB60R165CP	IPD040N03L G
IPB039N10N3 G	IPB107N20N3 G	IPB60R199CP	IPD042P03L3 G

Multisim 14.0 Power Pro Components

IPD048N06L3 G	IPD170N04N G	IPD60R2K0C6	IPI032N06N3 G
IPD050N03L G	IPD180N10N3 G	IPD60R380C6	IPI034NE7N3 G
IPD053N06N	IPD200N15N3 G	IPD60R520C6	IPI037N06L3 G
IPD053N06N3 G	IPD220N06L3 G	IPD60R600C6	IPI037N08N3 G
IPD053N08N3 G	IPD230N06N G	IPD60R600E6	IPI040N06N3 G
IPD060N03L G	IPD250N06N3 G	IPD60R950C6	IPI041N12N3 G
IPD068N10N3 G	IPD25CN10N G	IPD640N06L G	IPI045N10N3 G
IPD068P03L3 G	IPD320N20N3 G	IPD65R190C7	IPI04CN10N G
IPD075N03L G	IPD33CN10N G	IPD65R225C7	IPI052NE7N3 G
IPD079N06L3 G	IPD350N06L G	IPD65R380C6	IPI057N08N3 G
IPD082N10N3 G	IPD400N06N G	IPD65R380E6	IPI070N08N3 G
IPD088N04L G	IPD50R1K4CE	IPD65R420CFD	IPI072N10N3 G
IPD088N06N3 G	IPD50R280CE	IPD65R420CFDA	IPI075N15N3 G
IPD090N03L G	IPD50R2K0CE	IPD65R600C6	IPI076N12N3 G
IPD096N08N3 G	IPD50R380CE	IPD65R600E6	IPI084N06L3 G
IPD105N03L G	IPD50R399CP	IPD65R660CFD	IPI086N10N3 G
IPD105N04L G	IPD50R3K0CE	IPD78CN10N G	IPI100N08N3 G
IPD110N12N3 G	IPD50R500CE	IPD800N06N G	IPI110N20N3 G
IPD122N10N3 G	IPD50R520CP	IPD90R1K2C3	IPI111N15N3 G
IPD127N06L G	IPD50R650CE	IPI020N06N	IPI126N10N3 G
IPD12CN10N G	IPD50R800CE	IPI023NE7N3 G	IPI139N08N3 G
IPD135N03L G	IPD50R950CE	IPI024N06N3 G	IPI147N12N3 G
IPD135N08N3 G	IPD530N15N3 G	IPI028N08N3 G	IPI180N10N3 G
IPD144N06N G	IPD600N25N3 G	IPI029N06N	IPI200N15N3 G
IPD160N04L G	IPD60R1K4C6	IPI030N10N3 G	IPI200N25N3 G

Multisim 14.0 Power Pro Components

IPI26CN10N G	IPP023NE7N3 G	IPP060N06N	IPP147N03L G
IPI320N20N3 G	IPP024N06N3 G	IPP062NE7N3 G	IPP147N12N3 G
IPI35CN10N G	IPP028N08N3 G	IPP065N03L G	IPP16CN10L G
IPI50CN10N G	IPP029N06N	IPP06CN10L G	IPP16CN10N G
IPI50R350CP	IPP030N10N3 G	IPP070N08N3 G	IPP180N10N3 G
IPI530N15N3 G	IPP032N06N3 G	IPP072N10N3 G	IPP200N15N3 G
IPI600N25N3 G	IPP034N03L G	IPP075N15N3 G	IPP200N25N3 G
IPI60R250CP	IPP034NE7N3 G	IPP076N12N3 G	IPP230N06L3 G
IPI80CN10N G	IPP037N06L3 G	IPP080N03L G	IPP260N06N3 G
IPI90R1K0C3	IPP037N08N3 G	IPP084N06L3 G	IPP26CN10N G
IPI90R1K2C3	IPP040N06N	IPP085N06L G	IPP320N20N3 G
IPI90R500C3	IPP040N06N3 G	IPP086N10N3 G	IPP50CN10N G
IPI90R800C3	IPP041N04N G	IPP08CN10L G	IPP50R140CP
IPL60R199CP	IPP041N12N3 G	IPP093N06N3 G	IPP50R190CE
IPL60R299CP	IPP042N03L G	IPP096N03L G	IPP50R199CP
IPL60R385CP	IPP045N10N3 G	IPP100N08N3 G	IPP50R250CP
IPL65R070C7	IPP048N12N3 G	IPP110N20N3 G	IPP50R280CE
IPL65R099C7	IPP04CN10N G	IPP110N20NA	IPP50R299CP
IPL65R130C7	IPP052N06L3 G	IPP111N15N3 G	IPP50R350CP
IPL65R195C7	IPP052NE7N3 G	IPP114N03L G	IPP50R380CE
IPL65R230C7	IPP055N03L G	IPP114N12N3 G	IPP50R399CP
IPP015N04N G	IPP057N06N3 G	IPP120N06N G	IPP50R500CE
IPP020N06N	IPP057N08N3 G	IPP126N10N3 G	IPP50R520CP
IPP023N04N	IPP05CN10L G	IPP12CN10L G	IPP530N15N3 G
IPP023N04N G	IPP05CN10N G	IPP139N08N3 G	IPP600N25N3 G

Multisim 14.0 Power Pro Components

IPP60R099C6	IPP65R110CFD	IPP90R500C3	IPW50R280CE
IPP60R099CP	IPP65R110CFDA	IPP90R800C3	IPW60R041C6
IPP60R125C6	IPP65R125C7	IPS031N03L G	IPW60R045CP
IPP60R125CP	IPP65R150CFDA	IPS040N03L G	IPW60R070C6
IPP60R160C6	IPP65R190C6	IPS050N03L G	IPW60R075CP
IPP60R165CP	IPP65R190C7	IPS060N03L G	IPW60R099C6
IPP60R190C6	IPP65R190CFD	IPS075N03L G	IPW60R099CP
IPP60R190E6	IPP65R190CFDA	IPS090N03L G	IPW60R125C6
IPP60R199CP	IPP65R190E6	IPS105N03L G	IPW60R125CP
IPP60R1K4C6	IPP65R225C7	IPS110N12N3 G	IPW60R160C6
IPP60R250CP	IPP65R280C6	IPS118N10N G	IPW60R165CP
IPP60R280C6	IPP65R280E6	IPS12CN10L G	IPW60R190C6
IPP60R280E6	IPP65R310CFD	IPS135N03L G	IPW60R190E6
IPP60R299CP	IPP65R310CFDA	IPS50R520CP	IPW60R199CP
IPP60R380C6	IPP65R380C6	IPT004N03L	IPW60R250CP
IPP60R380E6	IPP65R380E6	IPT007N06N	IPW60R280C6
IPP60R385CP	IPP65R420CFD	IPT020N10N3	IPW60R280E6
IPP60R520C6	IPP65R600C6	IPT059N15N3	IPW65R019C7
IPP60R520E6	IPP65R600E6	IPU135N08N3 G	IPW65R037C6
IPP60R600C6	IPP65R660CFD	IPU50R1K4CE	IPW65R041CFD
IPP60R600E6	IPP65R660CFDA	IPU50R2K0CE	IPW65R045C7
IPP60R950C6	IPP80CN10N G	IPU50R3K0CE	IPW65R048CFDA
IPP65R045C7	IPP90R1K0C3	IPU50R950CE	IPW65R065C7
IPP65R065C7	IPP90R1K2C3	IPW50R190CE	IPW65R070C6
IPP65R095C7	IPP90R340C3	IPW50R199CP	IPW65R080CFD

Multisim 14.0 Power Pro Components

IPW65R080CFDA	IR2101PBF	IR2117SPBF	IRC530
IPW65R095C7	IR2101SPBF	IR2118PBF	IRC740
IPW65R110CFDA	IR2102PBF	IR2118SPBF	IRC830
IPW65R125C7	IR2102SPBF	IR2127PBF	IRCZ34
IPW65R150CFDA	IR2103PBF	IR2127SPBF	IRCZ44
IPW65R190C6	IR2103SPBF	IR2128PBF	IRF1010N
IPW65R190C7	IR2104PBF	IR2128SPBF	IRF1010NS
IPW65R190CFDA	IR2104SPBF	IR21363JPBF	IRF1010ZPBF
IPW65R190E6	IR2106PBF	IR21363PBF	IRF1010ZSPBF
IPW65R280C6	IR2106SPBF	IR21363SPBF	IRF1010ZSTRLPBF
IPW65R280E6	IR21084PBF	IR21365PBF	IRF1010ZSTRRPBF
IPW90R120C3	IR21084SPBF	IR21365SPBF	IRF120
IPW90R1K0C3	IR2108PBF	IR2136JPBF	IRF121
IPW90R1K2C3	IR2108SPBF	IR2136PBF	IRF122
IPW90R340C3	IR21094PBF	IR2136SPBF	IRF123
IPW90R500C3	IR21094SPBF	IR2181PBF	IRF131
IPW90R800C3	IR2109PBF	IR2181SPBF	IRF1310
IPZ65R019C7	IR2109SPBF	IR2183PBF	IRF132
IPZ65R045C7	IR2110PBF	IR2183SPBF	IRF1324S-7PPBF
IPZ65R065C7	IR2110SPBF	IR2184PBF	IRF1324STRL-7PP
IPZ65R095C7	IR2112PBF	IR2184SPBF	IRF133
IR2010PBF	IR2112SPBF	IR2301PBF	IRF140
IR2010S	IR2113PBF	IR2301SPBF	IRF1404ZPBF
IR2010SPBF	IR2113SPBF	IR2302PBF	IRF141
IR2011PBF	IR2117PBF	IR2302SPBF	IRF142

Multisim 14.0 Power Pro Components

IRF143	IRF255	IRF360	IRF453
IRF151	IRF2804PBF	IRF362	IRF460
IRF152	IRF2804SPBF	IRF3704ZSPBF	IRF462
IRF153	IRF2804STRLPBF	IRF3707ZSPBF	IRF510
IRF220	IRF2804STRRPBF	IRF3709ZSTRRPBF	IRF511
IRF221	IRF2903ZSPBF	IRF3710	IRF512
IRF222	IRF2903ZSTRLP	IRF3710S	IRF513
IRF223	IRF320	IRF3805S-7PPBF	IRF520
IRF231	IRF3205	IRF3805STRL-7PP	IRF520N
IRF232	IRF3205S	IRF4104PBF	IRF520NS
IRF233	IRF321	IRF420	IRF521
IRF234	IRF322	IRF421	IRF5210
IRF235	IRF323	IRF422	IRF5210S
IRF240	IRF330	IRF423	IRF522
IRF241	IRF331	IRF430	IRF523
IRF242	IRF332	IRF431	IRF530
IRF243	IRF333	IRF432	IRF530S
IRF244	IRF340	IRF433	IRF530S5
IRF245	IRF341	IRF440	IRF530CF
IRF250	IRF342	IRF441	IRF530N
IRF250S5	IRF343	IRF442	IRF530NS
IRF251	IRF350	IRF443	IRF531
IRF252	IRF351	IRF450	IRF532
IRF253	IRF352	IRF451	IRF533
IRF254	IRF353	IRF452	IRF540

Multisim 14.0 Power Pro Components

IRF540CF	IRF642	IRF6727MTRPBF	IRF7403
IRF540N	IRF643	IRF6775MTRPBF	IRF7404
IRF540NS	IRF644	IRF6785MTRPBF	IRF741
IRF541	IRF645	IRF6795MTRPBF	IRF7413
IRF542	IRF6613TRPBF	IRF6797MTRPBF	IRF742
IRF543	IRF6614TRPBF	IRF6798MTRPBF	IRF743
IRF610	IRF6616TRPBF	IRF6810STRPBF	IRF7495PBF
IRF611	IRF6641TRPBF	IRF6811STRPBF	IRF7495TRPBF
IRF612	IRF6643TRPBF	IRF6893MTRPBF	IRF7739L1TRPBF
IRF613	IRF6644TRPBF	IRF6894MTRPBF	IRF7748L1TRPBF
IRF614	IRF6645TRPBF	IRF6898MTRPBF	IRF7749L1TRPBF
IRF620	IRF6646TRPBF	IRF710	IRF7759L2TRPBF
IRF6201PBF	IRF6648TRPBF	IRF711	IRF7769L1TRPBF
IRF6201TRPBF	IRF6655TRPBF	IRF712	IRF7779L2TRPBF
IRF621	IRF6668TRPBF	IRF713	IRF7799L2TRPBF
IRF622	IRF6674TRPBF	IRF720	IRF7815PBF
IRF623	IRF6710S2TRPBF	IRF7201	IRF7815TRPBF
IRF624	IRF6711STRPBF	IRF721	IRF7855PBF
IRF625	IRF6712STRPBF	IRF722	IRF7855TRPBF
IRF631	IRF6713STRPBF	IRF723	IRF7907PBF
IRF632	IRF6714MTRPBF	IRF730	IRF7907TRPBF
IRF633	IRF6715MTRPBF	IRF731	IRF7946TRPBF
IRF634	IRF6716MTRPBF	IRF732	IRF821
IRF635	IRF6717MTRPBF	IRF733	IRF822
IRF641	IRF6718L2TRPBF	IRF740	IRF823

Multisim 14.0 Power Pro Components

IRF830	IRF9140	IRF9362TRPBF	IRF9620
IRF8302MTRPBF	IRF9141	IRF9383MTRPBF	IRF9620S
IRF8327STRPBF	IRF9142	IRF9389PBF	IRF9621
IRF832R	IRF9143	IRF9389TRPBF	IRF9622
IRF840	IRF9230	IRF9395MTRPBF	IRF9623
IRF841	IRF9231	IRF9510	IRF9630
IRF842	IRF9232	IRF9511	IRF9630S
IRF843	IRF9233	IRF9512	IRF9631
IRF8513TRPBF	IRF9240	IRF9513	IRF9632
IRF8707PBF	IRF9241	IRF9520	IRF9633
IRF8707TRPBF	IRF9242	IRF9521	IRF9640
IRF8714PBF	IRF9243	IRF9522	IRF9640S
IRF8714TRPBF	IRF9310PBF	IRF9523	IRF9641
IRF8721PBF	IRF9310TRPBF	IRF9530	IRF9642
IRF8721TRPBF	IRF9317PBF	IRF9530S	IRF9643
IRF8734PBF	IRF9317TRPBF	IRF9531	IRF9Z14
IRF8734TRPBF	IRF9321PBF	IRF9532	IRF9Z24
IRF8736PBF	IRF9321TRPBF	IRF9533	IRF9Z34
IRF8736TRPBF	IRF9328PBF	IRF9540	IRFAC40R
IRF8788PBF	IRF9328TRPBF	IRF9540S	IRFB3004PBF
IRF8788TRPBF	IRF9333PBF	IRF9541	IRFB3006PBF
IRF9130	IRF9333TRPBF	IRF9542	IRFB3077PBF
IRF9131	IRF9335PBF	IRF9543	IRFB3206PBF
IRF9132	IRF9335TRPBF	IRF9610	IRFB3207ZPBF
IRF9133	IRF9362PBF	IRF9610S	IRFB3256PBF

Multisim 14.0 Power Pro Components

IRFB3306PBF	IRFB7545PBF	IRFD9210	IRFF231
IRFB3307ZPBF	IRFB7546PBF	IRFD9220	IRFF232
IRFB4020PBF	IRFBC30	IRFD9223	IRFF233
IRFB4110PBF	IRFBC40	IRFE130	IRFF310
IRFB4115PBF	IRFBE20	IRFF110	IRFF311
IRFB4137PBF	IRFBE30	IRFF111	IRFF312
IRFB4227PBF	IRFBF20	IRFF112	IRFF313
IRFB4229PBF	IRFBF30	IRFF113	IRFF320
IRFB4310ZPBF	IRFBG30	IRFF120	IRFF321
IRFB4321PBF	IRFD110	IRFF121	IRFF322
IRFB4332PBF	IRFD113	IRFF122	IRFF323
IRFB4610PBF	IRFD120	IRFF123	IRFF330
IRFB4615PBF	IRFD123	IRFF130	IRFF331
IRFB4620PBF	IRFD120	IRFF131	IRFF332
IRFB5615PBF	IRFD123	IRFF132	IRFF333
IRFB5620PBF	IRFD210	IRFF133	IRFF420
IRFB7430PBF	IRFD213	IRFF210	IRFF421
IRFB7434PBF	IRFD220	IRFF211	IRFF422
IRFB7437PBF	IRFD223	IRFF212	IRFF423
IRFB7440PBF	IRFD9014	IRFF213	IRFF430
IRFB7446PBF	IRFD9024	IRFF220	IRFF431
IRFB7530PBF	IRFD9110	IRFF221	IRFF432
IRFB7534PBF	IRFD9113	IRFF222	IRFF433
IRFB7537PBF	IRFD9120	IRFF223	IRFF9121
IRFB7540PBF	IRFD9123	IRFF230	IRFF9122

Multisim 14.0 Power Pro Components

IRFF9123	IRFH5025TRPBF	IRFHM792TRPBF	IRFI840G
IRFF9130	IRFH5106TRPBF	IRFHM8235TRPBF	IRFI840GLC
IRFF9131	IRFH5110TRPBF	IRFHM830DTRPBF	IRFIZ44N
IRFF9132	IRFH5204TRPBF	IRFHM830TRPBF	IRFIZ46N
IRFF9133	IRFH5206TRPBF	IRFHM831TRPBF	IRFIZ48N
IRFF9220	IRFH5207TRPBF	IRFHM8326TRPBF	IRFJ140
IRFF9221	IRFH5210TRPBF	IRFHM8330TRPBF	IRFL9014
IRFF9222	IRFH5215TRPBF	IRFHM8334TRPBF	IRFL9110
IRFF9223	IRFH5301TRPBF	IRFHM8337TRPBF	IRFM140
IRFF9230	IRFH5302TRPBF	IRFHM8363TRPBF	IRFM150
IRFF9231	IRFH5304TRPBF	IRFHM9391TRPBF	IRFM9140
IRFF9232	IRFH5406TRPBF	IRFHS8242TRPBF	IRFML8244TRPBF
IRFF9233	IRFH6200TRPBF	IRFHS8342TRPBF	IRFN054
IRFG110	IRFH7107TRPBF	IRFHS9301TRPBF	IRFP044
IRFH4201TRPBF	IRFH7185TRPBF	IRFHS9351TRPBF	IRFP044N
IRFH4210DTRPBF	IRFH8201TRPBF	IRFI1010N	IRFP048N
IRFH4210TRPBF	IRFH8318TRPBF	IRFI3306GPBF	IRFP054
IRFH4213DTRPBF	IRFH8324TRPBF	IRFI3710	IRFP054N
IRFH4213TRPBF	IRFH8325TRPBF	IRFI4410ZPBF	IRFP064
IRFH4234TRPBF	IRFH8330TRPBF	IRFI520N	IRFP064N
IRFH4251DTRPBF	IRFH8334TRPBF	IRFI5210	IRFP140
IRFH4253DTRPBF	IRFH8337TRPBF	IRFI5305	IRFP140N
IRFH5006TRPBF	IRFHM4226TRPBF	IRFI530N	IRFP141
IRFH5010TRPBF	IRFHM4231TRPBF	IRFI540N	IRFP150
IRFH5020TRPBF	IRFHM4234TRPBF	IRFI7536GPBF	IRFP151

Multisim 14.0 Power Pro Components

IRFP152	IRFP4332PBF	IRFPE40	IRFR3910
IRFP153	IRFP4368PBF	IRFPE50	IRFR4105
IRFP240	IRFP440	IRFPF30	IRFR4105ZPBF
IRFP241	IRFP441	IRFPF40	IRFR4105ZTRPBF
IRFP2410	IRFP4468PBF	IRFPF50	IRFR48ZPBF
IRFP244	IRFP451	IRFPG30	IRFR48ZTRLPBF
IRFP245	IRFP452	IRFPG40	IRFR48ZTRPBF
IRFP250	IRFP4568PBF	IRFPG42	IRFR825PBF
IRFP251	IRFP462	IRFPG50	IRFR825TRPBF
IRFP252	IRFP4668PBF	IRFR110	IRFR9014
IRFP253	IRFP4768PBF	IRFR120	IRFR9024
IRFP254	IRFP5210	IRFR1205	IRFR9110
IRFP260	IRFP7430PBF	IRFR120N	IRFR9210
IRFP264	IRFP7530PBF	IRFR120ZPBF	IRFR9220
IRFP2907ZPBF	IRFP7537PBF	IRFR120ZTRPBF	IRFS1Z0
IRFP3006PBF	IRFP9140	IRFR121	IRFS3004-7PPBF
IRFP340	IRFP9141	IRFR210	IRFS3004PBF
IRFP341	IRFP9142	IRFR222	IRFS3004TRL7PP
IRFP350	IRFP9240	IRFR2307ZPBF	IRFS3004TRLPBF
IRFP351	IRFP9241	IRFR2307ZTRLPBF	IRFS3006-7PPBF
IRFP352	IRFP9242	IRFR2607ZPBF	IRFS3006TRL7PP
IRFP353	IRFP9243	IRFR2607ZTRPBF	IRFS3107-7PPBF
IRFP360	IRFPC30	IRFR3704ZPBF	IRFS3107TRL7PP
IRFP362	IRFPC40	IRFR3704ZTRLPBF	IRFS3206PBF
IRFP3710	IRFPE30	IRFR3704ZTRPBF	IRFS3206TRRPBF

Multisim 14.0 Power Pro Components

IRFS3207ZPBF	IRFS7434TRL7PP	IRFU3710ZPBF	IRG4BC20FDPBF
IRFS3306PBF	IRFS7434TRLPBF	IRFU3910	IRG4BC20SDPBF
IRFS3306TRLPBF	IRFS7530PBF	IRFU4105	IRG4BC20SD-SPBF
IRFS3307ZPBF	IRFS7530TRLPBF	IRFU4105ZPBF	IRG4BC20U
IRFS3307ZTRLPBF	IRFS7534PBF	IRFU48ZPBF	IRG4BC20UDPBF
IRFS3307ZTRRPBF	IRFS7534TRLPBF	IRFU9210	IRG4BC20UPBF
IRFS4010-7PPBF	IRFS7537PBF	IRFZ14	IRG4BC30FPBF
IRFS4010PBF	IRFS7537TRLPBF	IRFZ24N	IRG4BC30KDPBF
IRFS4010TRL7PP	IRFS7540PBF	IRFZ24NS	IRG4BC30UDPBF
IRFS4010TRLPBF	IRFS7540TRLPBF	IRFZ34	IRG4BC30UPBF
IRFS4010TRRPBF	IRFSL3004PBF	IRFZ34N	IRG4BC40S
IRFS4115PBF	IRFSL4115PBF	IRFZ44	IRG4BC40SPBF
IRFS4115TRLPBF	IRFSL7430PBF	IRFZ44N	IRG4BC40U
IRFS4127PBF	IRFSL7530PBF	IRFZ44NS	IRG4BC40UPBF
IRFS4127TRLPBF	IRFSL7534PBF	IRFZ46N	IRG4BC40W
IRFS4227PBF	IRFSL7537PBF	IRFZ46NS	IRG4BC40WPBF
IRFS4227TRLPBF	IRFSL7540PBF	IRFZ48N	IRG4MC30F
IRFS4321-7PPBF	IRFU110	IRFZ48NS	IRG4MC40U
IRFS4321TRL7PP	IRFU120	IRFZ48ZSPBF	IRG4MC50F
IRFS7430-7PPBF	IRFU1205	IRG4BC10KDPBF	IRG4MC50U
IRFS7430PBF	IRFU120N	IRG4BC10U	IRG4PC30KDPBF
IRFS7430TRL7PP	IRFU121	IRG4BC10UD	IRG4PC30KPBF
IRFS7430TRLPBF	IRFU210	IRG4BC10UDPBF	IRG4PC30U
IRFS7434-7PPBF	IRFU222	IRG4BC15UD	IRG4PC30UDPBF
IRFS7434PBF	IRFU2605	IRG4BC15UDPBF	IRG4PC30UPBF

Multisim 14.0 Power Pro Components

IRG4PC40FPBF	IRG4RC10UD	IRGBC20F	IRGKI140U06
IRG4PC40SPBF	IRG4RC10UDPBF	IRGBC20FD2	IRGKI165F06
IRG4PC40UD-EPBF	IRG4RC10UDTRLP	IRGBC20K	IRGKIN050M12
IRG4PC40UDPBF	IRG4RC10UDTRP	IRGBC20KD2	IRGKIN075M12
IRG4PC40UPBF	IRG4RC10UDTRRP	IRGBC20MD2	IRGLC60KD1
IRG4PC50FD-EPBF	IRG4RC10UTRPBF	IRGBC20MD2-S	IRGNI165F06
IRG4PC50FDPBF	IRG4RC20FPBF	IRGBC20S	IRGNI200F06
IRG4PC50KDPBF	IRG4RC20FTRLPBF	IRGBC20U	IRGNIN050M12
IRG4PC50KPBF	IRG4RC20FTRPBF	IRGBC20UD2	IRGNIN075M12
IRG4PC50SPBF	IRG7PH46UD-EP	IRGBC30F	IRGP20B120UD-EP
IRG4PC50UD-EPBF	IRG7PH46UDPBF	IRGBC30FD2	IRGP30B120KD-EP
IRG4PC50UDPBF	IRG7PH46U-EP	IRGBC30K	IRGP30B60KD-EP
IRG4PC50UPBF	IRG7PH46UPBF	IRGBC30KD2	IRGP4062D-EPBF
IRG4PC50WPBF	IRG7PSH73K10PBF	IRGBC30MD2	IRGP4062DPBF
IRG4PF50WPBF	IRGB15B60KDPBF	IRGBC30MD2-S	IRGP4063D-EPBF
IRG4PH20KPBF	IRGB20B60PD1PBF	IRGBC30S	IRGP4063DPBF
IRG4PH50SPBF	IRGB30B60KPBF	IRGBC30U	IRGP4068D-EPBF
IRG4PH50UDPBF	IRGB4045DPBF	IRGBC30UD2	IRGP4068DPBF
IRG4PH50UPBF	IRGB4059DPBF	IRGBC40F	IRGP420U
IRG4PSC71KDPBF	IRGB4060DPBF	IRGBC40K	IRGP50B60PD1PBF
IRG4PSC71KPBF	IRGB4061DPBF	IRGBC40S	IRGPC20F
IRG4PSC71UPBF	IRGB4062DPBF	IRGBC40U	IRGPC20U
IRG4RC10K	IRGB4B60KD1PBF	IRGBF20F	IRGPC30F
IRG4RC10KD	IRGB5B120KDPBF	IRGBF30F	IRGPC30FD2
IRG4RC10U	IRGB8B60KPBF	IRGKI115U06	IRGPC30K

Multisim 14.0 Power Pro Components

IRGPC30KD2	IRGPH40K	IRL2203S	IRL6342TRPBF
IRGPC30MD2	IRGPH50F	IRL2505	IRL7833SPBF
IRGPC30UD2	IRGPH50FD2	IRL2505S	IRL7833STRLPBF
IRGPC40F	IRGPH50K	IRL2703	IRL8113PBF
IRGPC40FD2	IRGPH50KD2	IRL2703S	IRL8113SPBF
IRGPC40K	IRGPH50M	IRL2910	IRL8113STRLPBF
IRGPC40KD2	IRGPH50MD2	IRL2910S	IRLB3034PBF
IRGPC40S	IRGPS40B120UDP	IRL3103	IRLB3036PBF
IRGPC40U	IRGPS60B120KDP	IRL3103S	IRLB8748PBF
IRGPC40UD2	IRGS15B60KDPBF	IRL3303	IRLD110
IRGPC50FD2	IRGS30B60KPBF	IRL3303S	IRLH5034TRPBF
IRGPC50K	IRGS4B60KD1PBF	IRL3705	IRLH5036TRPBF
IRGPC50KD2	IRGS8B60KPBF	IRL3705N	IRLHM620TRPBF
IRGPC50M	IRGS8B60KTRLPBF	IRL3705NS	IRLHS2242TRPBF
IRGPC50MD2	IRGSL15B60KDPBF	IRL3803	IRLHS6242TRPBF
IRGPC50S	IRGSL30B60KPBF	IRL3803S	IRLHS6276TRPBF
IRGPC5UD	IRGSL4B60KD1PBF	IRL510	IRLHS6342TRPBF
IRGPC60KD1	IRGTI165F06	IRL520	IRLHS6376TRPBF
IRGPF30F	IRGTI200F06	IRL530	IRLI2203G
IRGPF40F	IRGTIN025M12	IRL530N	IRLI2203N
IRGPF50F	IRGTIN050M12	IRL530NS	IRLI2505
IRGPH20M	IRGTIN075M12	IRL540	IRLI2703
IRGPH20S	IRL1404ZPBF	IRL6283MTRPBF	IRLI2910
IRGPH40F	IRL2203	IRL6297SDTRPBF	IRLI3103
IRGPH40FD2	IRL2203NS	IRL6342PBF	IRLI3303

Multisim 14.0 Power Pro Components

IRLI3803	IRLR2905	IRLR8726TRLPBF	IRLZ14
IRLI530N	IRLR2905ZPBF	IRLR8726TRPBF	IRLZ24
IRLIZ24N	IRLR2905ZTRLPBF	IRLR8729PBF	IRLZ34
IRLIZ34N	IRLR2905ZTRPBF	IRLR8729TRLPBF	IRLZ34N
IRLL3303	IRLR3103	IRLR8729TRPBF	IRLZ34NS
IRLML0030TRPBF	IRLR3110ZPBF	IRLR8743PBF	IRLZ44
IRLML0040TRPBF	IRLR3110ZTRLPBF	IRLR8743TRLPBF	IRLZ44N
IRLML0060TRPBF	IRLR3110ZTRPBF	IRLR8743TRPBF	ISO120BG
IRLML0100TRPBF	IRLR3110ZTRRPBF	IRLS4030-7PPBF	ISO120G
IRLML2030TRPBF	IRLR3303	IRLS4030PBF	ISO120SG
IRLML2060TRPBF	IRLR3636PBF	IRLS4030TRL7PP	ISO121BG
IRLML2244TRPBF	IRLR3636TRLPBF	IRLS4030TRLPBF	ISO121G
IRLML6244TRPBF	IRLR3636TRPBF	IRLSL4030PBF	ISO130P
IRLML6246TRPBF	IRLR3705ZPBF	IRLTS2242TRPBF	ISO130PB
IRLML6346TRPBF	IRLR3705ZTRPBF	IRLU024N	IVC102P
IRLML9301TRPBF	IRLR3717PBF	IRLU2703	IVC102U
IRLML9303TRPBF	IRLR3717TRPBF	IRLU2705	J105
IRLP150	IRLR3717TRRPBF	IRLU2905	J106
IRLP2203	IRLR6225PBF	IRLU2905ZPBF	J107
IRLP2505	IRLR6225TRPBF	IRLU3103	J108
IRLP3705	IRLR7807ZPBF	IRLU3110ZPBF	J109
IRLP3803	IRLR7807ZTRPBF	IRLU3303	J110
IRLR024N	IRLR8256PBF	IRLU3636PBF	J111
IRLR2703	IRLR8256TRPBF	IRLU3705ZPBF	J112
IRLR2705	IRLR8726PBF	IRLU8743PBF	J113

Multisim 14.0 Power Pro Components

J174	J310	JK_FF_NEGSR	L64210GC-20
J175	J401	KT88	L64210JC-15
J176	J402	L2081	L64210JC-20
J177	J403	L2082	L64210NC-15
J201	J404	L2083	L64210NC-20
J202	J405	L6201_SO20	L64211GC-15
J210	J406	L6201P_SO20	L64211GC-20
J211	J410	L6202_DIP18	L64211NC-15
J212	J411	L6203_ZIP11	L64211NC-20
J2N5902	J412	L6205_DIP20	L6911C_SO20
J2N5904	JAN2N2907A	L6205_SO20	L6911D_SO20
J2N5905	JAN2N3700	L6206_DIP24	L6911E_SO20
J2N5906	JAN2N4029	L6206_SO24	L88008
J2N5907	JAN2N4033	L6206P_SO36	L88012
J2N5908	JANTX2N2907A	L6207_DIP24	L88016
J2N5909	JANTX2N3700	L6207_SO24	LA_CARRY_GEN
J2N5911	JANTX2N4029	L6207P_SO36	LA_CARRY_GEN
J2N5912	JANTX2N4033	L6208_DIP24	LAMP
J2N6483	JANTXV2N2907A	L6208_SO24	LAMP_VIRTUAL
J2N6484	JANTXV2N3700	L6208P_SO36	LATCH_D
J2N6485	JANTXV2N4029	L6234_DIP20	LATCH_D2
J304	JANTXV2N4033	L6234P_SO20	LATCH_D4_SR_OE
J305	JFET_N	L6375_DIP8	LATCH_SR
J308	JFET_P	L6375_SO20	LATTICE-
J309	JK_FF	L64210GC-15	ispDOWNLOAD- HDR

Multisim 14.0 Power Pro Components

LATTICE- ispDOWNLOAD- USB-HDR	LED_ir	LF347BN	LF357AH
	LED_orange	LF347D	LF357BN
LC03-6R2G	LED_red	LF347M	LF357H
LCD_DISPLAY_08x1	LED_RED_RATED	LF347N	LF357M
LCD_DISPLAY_08x2	LED_yellow	LF351D	LF357N
LCD_DISPLAY_10x2	LED_YELLOW_RATE D	LF351M	LF400
LCD_DISPLAY_16x1		LF351N	LF401ACD
LCD_DISPLAY_16x2	LF13741H	LF351P	LF411ACH
LCD_DISPLAY_16x4	LF147D/883	LF353D	LF411ACN
LCD_DISPLAY_20x2	LF147J	LF353H	LF411AMH
LCD_DISPLAY_20x4	LF147J/883	LF353M	LF411CD
LCD_DISPLAY_24x2	LF155AH	LF353N	LF411CH
LCD_DISPLAY_30x2	LF155AH/883	LF353P	LF411CJG
LCD_DISPLAY_32x2	LF155H	LF355AH	LF411CN
LCD_DISPLAY_40x2	LF155H/883	LF355BM	LF411CP
LCD_DISPLAY_4DIGI T	LF156AH	LF355BN	LF411ID
	LF156AH/883	LF355H	LF411IP
LD102A	LF156H	LF355M	LF411MH
LD103A	LF156H/883	LF355N	LF411MH/883
LD106	LF157AH/883	LF356AH	LF411MWG/883
LED	LF157H/883	LF356BM	LF412ACH
LED_blue	LF255H	LF356BN	LF412ACN
LED_BLUE_RATED	LF256H	LF356H	LF412AMH
LED_green	LF257H	LF356M	LF412CD
LED_GREEN_RATED	LF347BD	LF356N	LF412CH

Multisim 14.0 Power Pro Components

LF412CJG	LF444ACN	LH0032G	LH0101K
LF412CN	LF444AMD	LH0032G/883	LH0101K-MIL
LF412CP	LF444CD	LH0041CG	LH1041G
LF412MH	LF444CJ	LH0041CJ	LH4161
LF412MH/883	LF444CM	LH0041G	LH4162
LF412MJ/883	LF444CN	LH0042CH	LHV870LC/NOPB
LF441ACH	LF444MD/883	LH0042H	LIMIT_NC
LF441ACN	LF451CM	LH0042H-MIL	LIMIT_NO
LF441AMH	LF453CM	LH0044ACH	LINKSYS-WRT54G-HD
LF441CD	LH0003CH	LH0044AH	LM101AD
LF441CH	LH0003H	LH0044BH	LM101AD/883
LF441CJ	LH0004CH	LH0044CH	LM101AF
LF441CM	LH0004H	LH0044H	LM101AF/883
LF441CN	LH0004H-MIL	LH0052CD	LM101AFK
LF441MH/883	LH0021CK	LH0052CH	LM101AFK/883
LF442ACH	LH0021K	LH0052D	LM101AH
LF442ACN	LH0022CD	LH0052H	LM101AH/883
LF442AMH	LH0022CH	LH0062CD	LM101AJ
LF442CD	LH0022D	LH0062CH	LM101AJ/883
LF442CH	LH0022H	LH0062D	LM101AJ-14
LF442CJ	LH0022H-MIL	LH0062H	LM101AJ-14/883
LF442CM	LH0024CH	LH0101ACK	LM101AJ8
LF442CN	LH0024H	LH0101AK	LM101AJG
LF442MH	LH0024H-MIL	LH0101AK-MIL	LM101AJG/883
LF442MH/883	LH0032CG	LH0101CK	

Multisim 14.0 Power Pro Components

LM101AP	LM108AD	LM109H	LM112H/883
LM101AU	LM108AH	LM109H/883	LM113-1H
LM101AU/883	LM108AH/883	LM109K	LM113-2H
LM101AW	LM108AJ	LM109K/883	LM117H
LM101AW/883	LM108AJ/883	LM10BH	LM117HVH
LM101D	LM108AJ-8	LM10BLH	LM117HVKSTL/883
LM101F	LM108AJ-8/883	LM10CH	LM117K
LM101F/883	LM108AJG	LM10CLH	LM118D
LM101H	LM108AL	LM10CLN	LM118FK
LM101H/883	LM108AP	LM10CLN8	LM118H
LM101J-14	LM108D	LM10CLWM	LM118H/883
LM101J-14/883	LM108D/883	LM10CN	LM118J
LM107H	LM108H	LM10CN8	LM118J/883
LM107H/883	LM108H/883	LM10CWM	LM118J8
LM107J	LM108J	LM10H	LM118J-8
LM107J/883	LM108J/883	LM10H/883	LM118J8/883
LM107J-14	LM108J8	LM111E	LM118J-8/883
LM107J-14/883	LM108J-8	LM111E/883	LM118JG
LM107J8	LM108J8/883	LM111FK	LM118L
LM107J8/883	LM108J-8/883	LM111H	LM118P
LM107JG	LM108JG	LM111J-14	LM119D
LM107JG/883	LM108JG/883	LM111J-8	LM119N
LM107U	LM108L	LM111JG	LM11CH
LM107W	LM108P	LM111W	LM11CLH
LM107W/883	LM108W/883	LM112H	LM11CLN

Multisim 14.0 Power Pro Components

LM11CN	LM124W	LM139AFK	LM148J
LM11H	LM124W/883	LM139AJ	LM148J/883
LM120H-12	LM129AH	LM139AW	LM149J
LM120H-15	LM129BH	LM139D	LM149J/883
LM120H-5	LM129CH	LM139E	LM1558H
LM120K-12/883	LM12CLK	LM139FK	LM1558H/883
LM120K-15/883	LM12LK	LM139J	LM1558J
LM120K-5/883	LM133K	LM139W	LM1558J/883
LM123K	LM13600AN	LM140AK-12/883	LM158AD
LM124AD	LM13600M	LM140AK-15/883	LM158AFK
LM124AE	LM13600N	LM140AK-5/883	LM158AH
LM124AE/883	LM136AH-2.5	LM140H-12/883	LM158AH/883
LM124AFK	LM136AH-5.0	LM140H-15/883	LM158AJ
LM124AJ	LM136H-2.5	LM140H-5/883	LM158AJ/883
LM124AJ/883	LM136H-5.0	LM143H	LM158AJG
LM124AN	LM13700AN	LM143H/883	LM158AN
LM124AW/883	LM13700M	LM144H	LM158AP
LM124AWG/883	LM13700N	LM144H/883	LM158AWG/883
LM124D	LM137H	LM1458H	LM158D
LM124E	LM137H/883	LM1458J	LM158FK
LM124E/883	LM137HVH/883	LM1458M	LM158H
LM124FK	LM137K/883	LM1458N	LM158H/883
LM124J	LM138K	LM146J	LM158J
LM124J/883	LM139AD	LM146J/883	LM158J/883
LM124N	LM139AE	LM148FK	LM158JG

Multisim 14.0 Power Pro Components

LM158N	LM208AN	LM221H	LM239D
LM158P	LM208AP	LM224AD	LM239DG
LM160H	LM208D	LM224AJ	LM239DR2G
LM160J	LM208H	LM224AN	LM239DTBR2G
LM160J-14	LM208J	LM224AP	LM239J
LM1875T	LM208J-8	LM224D	LM239N
LM1877M-9	LM208N	LM224DG	LM239NG
LM1877N-9	LM208P	LM224DR2G	LM246J
LM193D	LM211D	LM224DTBG	LM248D
LM193FK	LM211H	LM224DTBR2G	LM248J
LM193JG	LM211J-8	LM224J	LM248N
LM193P	LM211M	LM224N	LM258AD
LM201AD	LM211P	LM224NG	LM258AH
LM201AH	LM211QD	LM224P	LM258AJG
LM201AN	LM212H	LM236AH-2.5	LM258AN
LM201AP	LM216AD	LM236AH-5.0	LM258AP
LM202H	LM216AF	LM236AM-2.5	LM258D
LM207D	LM216AH	LM236AZ-5.0	LM258DG
LM207H	LM216D	LM236H-2.5	LM258DMR2G
LM207J	LM216F	LM236H-5.0	LM258DR2G
LM207P	LM216H	LM236M-2.5	LM258H
LM208AD	LM218D	LM236Z-2.5	LM258JG
LM208AH	LM218H	LM239AD	LM258N
LM208AJ	LM218JG	LM239AJ	LM258NG
LM208AJ-8	LM218P	LM239AN	LM258P

Multisim 14.0 Power Pro Components

LM285AM-1.2	LM2902N	LM2904D	LM2931CS
LM2878P	LM2902NG	LM2904DG	LM2931CT
LM2900N	LM2902VD	LM2904DMR2G	LM2931M-5
LM2901D	LM2902VDG	LM2904DR2G	LM2931S-5
LM2901DBR	LM2902VDR2G	LM2904ITP	LM2931T-5
LM2901DG	LM2902VDTBG	LM2904M	LM2931Z-5
LM2901DR2G	LM2902VDTBR2G	LM2904N	LM293AD
LM2901DTBR2G	LM2902VN	LM2904NG	LM293AP
LM2901J	LM2903D	LM2904P	LM293D
LM2901M	LM2903DG	LM2904PW	LM293DG
LM2901MX	LM2903DMR2G	LM2904QD	LM293DMR2G
LM2901N	LM2903DR2	LM2904QP	LM293DR2G
LM2901NG	LM2903DR2G	LM2904VD	LM293P
LM2901NS	LM2903J	LM2904VDG	LM2940T-10
LM2901PWR	LM2903M	LM2904VDMR2G	LM2940T-5
LM2901VDG	LM2903MX	LM2904VDR2G	LM301AD
LM2901VDR2G	LM2903N	LM2904VN	LM301AH
LM2901VDTBR2G	LM2903NG	LM2904VNG	LM301AJ
LM2901VNG	LM2903P	LM2924M	LM301AJ8
LM2902DG	LM2903PW	LM2924N	LM301AN
LM2902DR2G	LM2903QD	LM2931AM-5	LM301AP
LM2902DTBG	LM2903QP	LM2931AS-5	LM3046M
LM2902DTBR2G	LM2904ADMR2G	LM2931AT-5	LM307D
LM2902M	LM2904AN	LM2931AZ-5	LM307H
LM2902MT	LM2904ANG	LM2931CM	LM307J8

Multisim 14.0 Power Pro Components

LM307N	LM313H	LM320T-15	LM324N
LM307P	LM317AH	LM320T-5	LM324NG
LM308AD	LM317H	LM321AH	LM324P
LM308AH	LM317K	LM321H	LM324PWLE
LM308AJ	LM317LM	LM323AK	LM324x2DBLE
LM308AJ-8	LM317LZ	LM324AD	LM329AH
LM308AN	LM318D	LM324ADG	LM329BH
LM308AN8	LM318H	LM324ADR2G	LM329BZ
LM308D	LM318J8	LM324ADTBG	LM329CH
LM308H	LM318J-8	LM324ADTBR2G	LM329CZ
LM308J	LM318M	LM324AJ	LM329DH
LM308J-8	LM318N	LM324AM	LM329DZ
LM308M	LM318N8	LM324AN	LM3301N
LM308N	LM318P	LM324ANG	LM3302D
LM308N8	LM318S8	LM324AP	LM3302J
LM309H	LM320H-12	LM324APWLE	LM3302N
LM309K	LM320H-15	LM324D	LM3303J
LM311D	LM320H-5	LM324DBLE	LM3303M
LM311H	LM320K-12	LM324DG	LM3303N
LM311M	LM320K-15	LM324DR2G	LM333K
LM311N	LM320K-5	LM324DTBG	LM333T
LM311N-14	LM320LZ-12	LM324DTBR2G	LM336BM-2.5
LM311P	LM320LZ-15	LM324J	LM336BM-5.0
LM311PWR	LM320LZ-5	LM324M	LM336BZ-2.5
LM312H	LM320T-12	LM324MT	LM336BZ-5.0

Multisim 14.0 Power Pro Components

LM336M-2.5	LM3401D	LM348M	LM359J
LM336M-5.0	LM3401P	LM348N	LM359M
LM336Z-2.5	LM3403J	LM348PW	LM359N
LM336Z-5.0	LM3403M	LM358AD	LM3875TF/NOPB
LM337H	LM3403N	LM358ADR2G	LM3900D
LM337K	LM340AT-12	LM358AH	LM3900M
LM337LM	LM340AT-15	LM358AJG	LM3900N
LM337LZ	LM340AT-5	LM358AM	LM393AD
LM338K	LM340K-12	LM358AN	LM393AH
LM339AD	LM340K-15	LM358AP	LM393AJ
LM339AJ	LM340K-5	LM358BP	LM393AP
LM339AM	LM340LAH-15	LM358D	LM393D
LM339AN	LM340LAH-5	LM358DB	LM393DG
LM339ANS	LM340LAZ-15	LM358DG	LM393DMR2G
LM339D	LM340LAZ-5	LM358DMR2G	LM393DR2G
LM339DBR	LM340T-18	LM358DR2G	LM393H
LM339DG	LM340T-6	LM358H	LM393J
LM339DR2G	LM340T-8	LM358J	LM393M
LM339DTBR2G	LM343H	LM358JG	LM393N
LM339J	LM344H	LM358M	LM393NG
LM339M	LM346J	LM358N	LM393P
LM339N	LM346M	LM358NG	LM393PW
LM339NG	LM346N	LM358P	LM4136CJ
LM339NS	LM348D	LM358PW	LM4136CM
LM339PWR	LM348J	LM358TP	LM4136CN

Multisim 14.0 Power Pro Components

LM4136J/883	LM607CN	LM6144BIN	LM6171BIM
LM4250CH	LM6118E/883	LM6152ACM	LM6171BIN
LM4250CM	LM6118J/883	LM6152BCM	LM6172AMJFQML
LM4250CN	LM6118N	LM6161E/883	LM6172AMWGFQ ML
LM4250H	LM6121H/883	LM6161J	LM6172IM
LM4250J	LM6121J/883	LM6161J/883	LM6172IN
LM4250J-MIL	LM6125H	LM6161W/883	LM6181AIN
LM4562HA	LM6125H/883	LM6161WG/883	LM6181IM
LM4562MA	LM6132AIM	LM6162E/883	LM6181IN
LM4562NA	LM6132AIN	LM6162J/883	LM6182AIN
LM4871LD	LM6132BIM	LM6162N	LM6182IN
LM4871M	LM6132BIN	LM6162W/883	LM6211MF
LM4871MM/NOPB	LM6134AIM	LM6162WG/883	LM6218AN
LM4871MX	LM6134AIN	LM6164E/883	LM6218AWM
LM555CM	LM6134BIM	LM6164J	LM6218N
LM555CN	LM6134BIN	LM6164J/883	LM6218WM
LM556CM	LM6142AIM	LM6164W/883	LM6221H
LM556CN	LM6142AIN	LM6164WG/883	LM6221N
LM607ACH	LM6142AMJ-MLS	LM6165E/883	LM6225N
LM607ACN	LM6142AMJ-QML	LM6165J	LM6261J
LM607AMH	LM6142BIM	LM6165J/883	LM6261M
LM607BCH	LM6142BIN	LM6165W/883	LM6261N
LM607BCN	LM6144AIM	LM6165WG/883	LM6262M
LM607BMH	LM6144AIN	LM6171AIM	LM6262N
LM607CH	LM6144BIM	LM6171AIN	

Multisim 14.0 Power Pro Components

LM6264J	LM6364M	LM7131ACN	LM7301IM5
LM6264N	LM6364N	LM7131BCM	LM7321MA
LM6265J	LM6365M	LM7131BCM5	LM7321MF
LM6265N	LM6365N	LM7131BCN	LM7322MA
LM627ACH	LM637ACH	LM715CH	LM7322MM
LM627AMH	LM637AMH	LM715CJ	LM7332MA
LM627BCH	LM637BCH	LM715MH	LM7332MM
LM627BMH	LM637BMH	LM715MJ	LM7341MF
LM627CH	LM637CH	LM7171AIM	LM7372IMA
LM627CN	LM637CN	LM7171AIN	LM7372MR
LM6310IM	LM675T	LM7171AIWM	LM741AH/883
LM6310IN	LM709AH	LM7171AMJFQML	LM741AJ-14/883
LM6311IM	LM709CH	LM7171BIM	LM741CH
LM6311IN	LM709CN	LM7171BIN	LM741CJ
LM6313N	LM709CN-8	LM7171BIWM	LM741CM
LM6317IM	LM709H	LM723CN	LM741CN
LM6317IN	LM710AMJ	LM723E	LM741EH
LM6321M	LM710AMW	LM723H	LM741EN
LM6321N	LM710CH	LM725AH	LM741H
LM6325N	LM710CN	LM725AH/883	LM741H/883
LM6361J	LM710H	LM725CH	LM741J
LM6361M	LM7121IM	LM725CN	LM741J/883
LM6361N	LM7121IM5	LM725H	LM741J-14/883
LM6362M	LM7131ACM	LM725H/883	LM741W/883
LM6362N	LM7131ACM5	LM7301IM	LM747AH

Multisim 14.0 Power Pro Components

LM747AJ	LM7818KC	LMC6001AIN	LMC6044AIM
LM747CH	LM7824CT	LMC6001BIH	LMC6044AIN
LM747CJ	LM7905CT	LMC6001BIN	LMC6044IM
LM747EJ	LM7909CT	LMC6022IM	LMC6044IN
LM747H	LM7912CT	LMC6022IN	LMC6061AIM
LM747J	LM7915CT	LMC6024IM	LMC6061AIN
LM748CH	LM7918CT	LMC6024IN	LMC6061AMJ/883
LM748CJ	LM7924CT	LMC6032IM	LMC6061AMN
LM748CN	LM8261M5	LMC6032IN	LMC6061IM
LM748H	LM8272MM	LMC6034IM	LMC6061IN
LM759CH	LM833D	LMC6034IN	LMC6062AIM
LM759CP	LM833DG	LMC6035IBP	LMC6062AIN
LM759H/883	LM833DR2G	LMC6035IM	LMC6062AMJ/883
LM759MH	LM833M	LMC6035IMM	LMC6062AMN
LM77000CP	LM833MM	LMC6035ITL	LMC6062IM
LM7805CT	LM833N	LMC6036IM	LMC6062IN
LM7805KC	LM833NG	LMC6036IMT	LMC6064AIM
LM7806KC	LM837M	LMC6041AIM	LMC6064AIN
LM7808KC	LM837N	LMC6041AIN	LMC6064AMJ/883
LM7809CT	LMC2001ACM5	LMC6041IM	LMC6064AMN
LM7812CT	LMC2001AIM	LMC6041IN	LMC6064IM
LM7812KC	LMC555CH	LMC6042AIM	LMC6064IN
LM7815CT	LMC555CM	LMC6042AIN	LMC6081AIM
LM7815KC	LMC555CN	LMC6042IM	LMC6081AIN
LM7818CT	LMC6001AIH	LMC6042IN	LMC6081AMN

Multisim 14.0 Power Pro Components

LMC6081IM	LMC6464AMWG-QML	LMC6494AEN	LMC662AIM
LMC6081IN		LMC6494BEM	LMC662AIN
LMC6082AIM	LMC6464BIM	LMC6494BEN	LMC662AMD
LMC6082AIN	LMC6464BIN	LMC6572AIM	LMC662AMJ/883
LMC6082AMN	LMC6464IM	LMC6572AIN	LMC662CM
LMC6082IM	LMC6464IN	LMC6572BIM	LMC662CN
LMC6082IN	LMC6482AIM	LMC6572BIN	LMC6681AIM
LMC6084AIM	LMC6482AIN	LMC6574AIM	LMC6681AIN
LMC6084AIN	LMC6482AMJ/883	LMC6574AIN	LMC6681BIM
LMC6084AMN	LMC6482IM	LMC6574BIM	LMC6681BIN
LMC6084IM	LMC6482IMM	LMC6574BIN	LMC6682AIM
LMC6084IN	LMC6482IN	LMC6582AIM	LMC6682AIN
LMC6442AIM	LMC6482MN	LMC6582AIN	LMC6682BIM
LMC6442IM	LMC6484AIM	LMC6582BIM	LMC6682BIN
LMC6442IN	LMC6484AIN	LMC6582BIN	LMC6684AIM
LMC6462AIM	LMC6484AMJ/883	LMC6584AIM	LMC6684AIN
LMC6462AIN	LMC6484AMWG/883	LMC6584AIN	LMC6684BIM
LMC6462AMN	LMC6484IM	LMC6584BIM	LMC6684BIN
LMC6462BIM	LMC6484IN	LMC6584BIN	LMC6762AIM
LMC6462BIN	LMC6484MN	LMC660AIM	LMC6762BIM
LMC6462IM	LMC6492AEM	LMC660AIN	LMC6772AIM
LMC6462IN	LMC6492AEN	LMC660AMD	LMC6772AIMM
LMC6464AIM	LMC6492BEM	LMC660AMJ/883	LMC6772BIM
LMC6464AIN	LMC6492BEN	LMC660CM	LMC6772BIN
LMC6464AMN	LMC6494AEM	LMC660CN	LMC7101AIM5

Multisim 14.0 Power Pro Components

LMC7101AIN	LME49720HA	LMH6554LE	LMH6642MFXEP
LMC7101BIM5	LME49720MA	LMH6555SQ	LMH6643MA
LMC7101BIN	LME49720NA	LMH6559MA	LMH6643MAXEP
LMC7111BIM5	LME49721MA/NOP B	LMH6559MF	LMH6643MM
LMC7211AIM	LME49740MA	LMH6601MG	LMH6644MA
LMC7211AIM5	LME49740NA	LMH6609MA	LMH6644MAXEP
LMC7211BIM	LME49990MA/NOP B	LMH6609MF	LMH6644MT
LMC7211BIM5		LMH6611MK	LMH6645MA
LMC7215IM	LMH6321MR	LMH6612MA	LMH6645MF
LMC7215IM5	LMH6321TS	LMH6618MK	LMH6646MA
LMC7221AIM	LMH6502MA	LMH6619MA	LMH6646MM
LMC7221AIM5	LMH6502MT	LMH6622MA	LMH6647MA
LMC7221BIM	LMH6503MA	LMH6622MM	LMH6647MF
LMC7221BIM5	LMH6503MT	LMH6624J-QML	LMH6655MA
LMC7225IM5	LMH6505MA	LMH6624MA	LMH6655MM
LMC8101BP	LMH6505MM	LMH6624MF	LMH6657MF
LMC8101MM	LMH6521SQ/NOPB	LMH6628JFQML	LMH6657MG
LMC8101TP	LMH6550MA	LMH6628MA	LMH6672MA
LME49600TS/NOPB	LMH6550MM	LMH6628WGFQML	LMH6672MR
LME49710HA	LMH6551MA	LMH6629MF	LMH6702J-QML
LME49710MA	LMH6551MM	LMH6629SD	LMH6702MA
LME49710NA	LMH6552MA	LMH6639MA	LMH6702MF
LME49713HA/NOP B	LMH6552SD	LMH6639MF	LMH6703MA
LME49713MA/NOP B	LMH6553MR	LMH6642MA	LMH6703MF
	LMH6553SD	LMH6642MF	LMH6714J-QML

Multisim 14.0 Power Pro Components

LMH6714MA	LMP2022MM	LMP7712MM	LMP8603QMA
LMH6714MF	LMP2231AMA	LMP7715MF	LMP8603QMM
LMH6715JFQML	LMP2231AMF	LMP7716MM	LMP8645HVMK
LMH6715MA	LMP2231BMA	LMP7717MA	LMP8645MK
LMH6718MA	LMP2231BMF	LMP7717MF	LMP8671MA/NOPB
LMH6720J-QML	LMP2232AMA	LMP7718MA	LMP8672MA/NOPB
LMH6720MA	LMP2232AMM	LMP7718MM	LMP8674MA/NOPB
LMH6720MF	LMP2232BMA	LMP7731MA	LMV2011MA
LMH6722J-QML	LMP2232BMM	LMP7731MF	LMV2011MF
LMH6722MA	LMP2234AMA	LMP7732MA	LMV321M5
LMH6722MT	LMP2234AMT	LMP7732MM	LMV321M7
LMH6723MA	LMP2234BMA	LMP8270MA	LMV324M
LMH6723MF	LMP2234BMT	LMP8271MA	LMV324MT
LMH6733MQ	LMP7300MA	LMP8272MA	LMV331M5
LMH6738MQ	LMP7300MM	LMP8275MA	LMV331M7
LMH6739MQ	LMP7701MA	LMP8276MA	LMV339M
LMP2011MA	LMP7701MF	LMP8277MA	LMV339MT
LMP2011MF	LMP7702MA	LMP8601MA	LMV342MA
LMP2015MA	LMP7702MM	LMP8601QMA	LMV342MM
LMP2015MF	LMP7704MA	LMP8602MA	LMV358M
LMP2016MA	LMP7704MT	LMP8602MM	LMV358MM
LMP2016MM	LMP7707MF	LMP8602QMA	LMV393M
LMP2021MA	LMP7708MM	LMP8602QMM	LMV393MM
LMP2021MF	LMP7709MT	LMP8603MA	LMV551MG
LMP2022MA	LMP7711MK	LMP8603MM	LMV552MM

Multisim 14.0 Power Pro Components

LMV554MT	LMV7291MG	LMV834MT	LMX324ASD+
LMV601MG/NOPB	LMV751M5	LMV841MG	LMX324AUD+
LMV602MA/NOPB	LMV761MA	LMV842MA	LMX358AKA+
LMV602MM/NOPB	LMV761MF	LMV842MM	LMX358ASA+
LMV604MA/NOPB	LMV771MG	LMV844MA	LMX358AUA+
LMV604MT/NOPB	LMV772MA	LMV844MT	LOG100JP
LMV611MF/NOPB	LMV772MM	LMV851MG	LOG101AID
LMV611MG/NOPB	LMV772QMM	LMV852MM	LOG102AID
LMV612MA/NOPB	LMV774MT	LMV854MT	LOG104AID
LMV612MM/NOPB	LMV791MK	LMV861MG	LOG112AID
LMV614MA/NOPB	LMV792MM	LMV862MM	LOG114AIRGVR
LMV614MT/NOPB	LMV793MA	LMV881LE/NOPB	LOSSLESS_LINE_TYP E1
LMV641MA	LMV793MF	LMV931MF	LOSSLESS_LINE_TYP E2
LMV641MG	LMV794MA	LMV931MG	LOSSY_TRANSMISSI ON_LINE
LMV651MG	LMV794MM	LMV932MA	LP111JG
LMV652MM	LMV796MF	LMV932MM	LP124J
LMV654MT	LMV797MM	LMV934MA	LP211D
LMV711M6	LMV821M5	LMV934MT	LP211JG
LMV716MM	LMV821M7	LMV951MK	LP211P
LMV7219M5	LMV822M	LMV981BL	LP239D
LMV7219M7	LMV822MM	LMV981MF	LP239J
LMV721M5	LMV824M	LMV981MG	LP239N
LMV721M7	LMV824MT	LMV981TL	LP2901D
LMV7271MF	LMV831MG	LMX321AUK+	
LMV7271MG	LMV832MM	LMX321AXK+	

Multisim 14.0 Power Pro Components

LP2901J	LPC662AIM	LPV324MT	LT1004IS8-1.2
LP2901N	LPC662AIN	LPV358MM	LT1004MH
LP2902M	LPC662AMD	LPV358MX	LT1006ACH
LP2902N	LPC662AMJ/883	LPV511MG	LT1006ACJ8
LP311D	LPC662IM	LPV521MG	LT1006AMH
LP311JG	LPC662IN	LT1001	LT1006AMJ8
LP311M	LPR200JC10	LT1001ACH	LT1006CH
LP311N	LPR200JC12	LT1001ACJ8	LT1006CJ8
LP311P	LPR200JC15	LT1001ACN8	LT1006CN8
LP324M	LPR200JC20	LT1001AMH/883	LT1006MH
LP324N	LPR200PC10	LT1001AMJ8/883	LT1006MJ8
LP339D	LPR200PC12	LT1001CH	LT1006S8
LP339J	LPR200PC15	LT1001CJ8	LT1007ACH
LP339M	LPR200PC20	LT1001CN8	LT1007ACJ8
LP339N	LPR201JC10	LT1001CS8	LT1007ACN8
LPC660AIM	LPR201JC12	LT1001MH	LT1007ACP
LPC660AIN	LPR201JC15	LT1001MJ8	LT1007AMH
LPC660AMD	LPR201JC20	LT1002ACJ	LT1007AMJ8
LPC660AMJ/883	LPR201PC10	LT1002ACN	LT1007AMJG
LPC660IM	LPR201PC12	LT1002AMJ	LT1007AML
LPC661AIM	LPR201PC15	LT1002CJ	LT1007AMP
LPC661AIN	LPR201PC20	LT1002CN	LT1007CDW
LPC661AMN	LPV321M5	LT1002MJ	LT1007CH
LPC661IM	LPV321M7	LT1004CH	LT1007CJ8
LPC661IN	LPV324M	LT1004CZ	LT1007CN8

Multisim 14.0 Power Pro Components

LT1007CP	LT1012AMH	LT1013DN8	LT1019ACH-2.5
LT1007CS	LT1012CH	LT1013DP	LT1019ACH-4.5
LT1007MH	LT1012CN8	LT1013IP	LT1019ACH-5
LT1007MJ8	LT1012DH	LT1013MFK	LT1019ACN8-10
LT1007MJG	LT1012DN8	LT1013MH	LT1019ACN8-2.5
LT1007ML	LT1012MH	LT1013MJ8	LT1019ACN8-4.5
LT1007MP	LT1012S8	LT1013MJG	LT1019ACN8-5
LT1008CH	LT1013ACH	LT1013MP	LT1019AMH-10
LT1008CN8	LT1013ACJ8	LT1014ACJ	LT1019AMH-2.5
LT1008MH	LT1013ACP	LT1014AMJ	LT1019AMH-4.5
LT1008S8	LT1013AIP	LT1014CJ	LT1019AMH-5
LT1009CH	LT1013AMFK	LT1014CN	LT1019CH-10
LT1009CZ	LT1013AMH	LT1014DN	LT1019CH-2.5
LT1009MH	LT1013AMJ8	LT1014MJ	LT1019CH-4.5
LT1009S8	LT1013AMP	LT1016CN8	LT1019CH-5
LT1010CDD	LT1013CH	LT1016CS8	LT1019CN8-10
LT1010CH	LT1013CJ8	LT1016IN8	LT1019CN8-2.5
LT1010CN8	LT1013CN8	LT1016IS8	LT1019CN8-4.5
LT1010CT	LT1013CP	LT1017CN8	LT1019CN8-5
LT1010MH	LT1013DD	LT1017CS8	LT1019CS8-10
LT1011CN8	LT1013DID	LT1017CSW	LT1019CS8-2.5
LT1011CS8	LT1013DIP	LT1018CN8	LT1019CS8-4.5
LT1012	LT1013DMD	LT1018CS8	LT1019CS8-5
LT1012ACH	LT1013DMJG	LT1018CSW	LT1019IN8-10
LT1012ACN8	LT1013DMP	LT1019ACH-10	LT1019IN8-2.5

Multisim 14.0 Power Pro Components

LT1019IN8-4.5	LT1028ACJ8	LT1037MH	LT1057IS
LT1019IN8-5	LT1028ACN8	LT1037MJ8	LT1057MH
LT1019MH-10	LT1028AMH	LT1037MJG	LT1057MJ8
LT1019MH-2.5	LT1028AMJ8	LT1037ML	LT1057S
LT1019MH-4.5	LT1028CH	LT1037MP	LT1058ACJ
LT1019MH-5	LT1028CJ8	LT1055ACH	LT1058ACN
LT1021BCH-5	LT1028CN8	LT1055AMH	LT1058AMJ
LT1021BCN8-10	LT1028CS	LT1055CH	LT1058CJ
LT1021BCN8-5	LT1028MH	LT1055CN8	LT1058CMJ
LT1021BCN8-7	LT1028MJ8	LT1055MH	LT1058CN
LT1021BMH-10	LT1037ACH	LT1055S8	LT1077ACH
LT1021DCS8-10	LT1037ACJ8	LT1056ACH	LT1077ACJ8
LT1021DCS8-5	LT1037ACN8	LT1056AMH	LT1077ACN8
LT1021DCS8-7	LT1037ACP	LT1056CH	LT1077AIN8
LT1022ACH	LT1037AMH	LT1056CN8	LT1077AMH
LT1022AMH	LT1037AMJ8	LT1056MH	LT1077AMJ8
LT1022CH	LT1037AMJG	LT1056S8	LT1077CH
LT1022CN8	LT1037AML	LT1057ACH	LT1077CJ8
LT1022MH	LT1037AMP	LT1057ACJ8	LT1077CN8
LT1024ACN	LT1037CDW	LT1057ACN8	LT1077IN8
LT1024AMD	LT1037CH	LT1057AMH	LT1077IS8
LT1024CN	LT1037CJ8	LT1057AMJ8	LT1077MH
LT1024MD	LT1037CN8	LT1057CH	LT1077MJ8
LT1028	LT1037CP	LT1057CJ8	LT1077S8
LT1028ACH	LT1037CS	LT1057CN8	LT1078ACH

Multisim 14.0 Power Pro Components

LT1078ACN8	LT1101AIN8	LT1122AMJ8	LT1167CN8
LT1078AMJ8	LT1101AMH	LT1122BCJ8	LT1167CS8
LT1078CN8	LT1101AMJ8	LT1122BCN8	LT1168CN8
LT1078IN8	LT1101CH	LT1122BMJ8	LT1168CS8
LT1078IS8	LT1101CJ8	LT1122CCJ8	LT1169CN8
LT1078MH	LT1101CN8	LT1122CCN8	LT1169CS8
LT1078MJ8	LT1101IN8	LT1122CMJ8	LT1178ACH
LT1078S8	LT1101MH	LT1122CS8	LT1178ACJ8
LT1079ACN	LT1101MJ8	LT1122DCJ8	LT1178ACN8
LT1079AM	LT1101S	LT1122DCN8	LT1178AMH
LT1079CN	LT1102ACN8	LT1122DMJ8	LT1178AMJ8
LT1079IN	LT1102CN8	LT1122DS8	LT1178CH
LT1079ISW	LT1102IN8	LT1124CN8	LT1178CJ8
LT1079MJ	LT1112S8	LT1124CS8	LT1178CN8
LT1079SW	LT1113ACN8	LT1125CN	LT1178IN8
LT1083CP	LT1113CS8	LT1125CSW	LT1178MH
LT1084CP	LT1114S	LT1126CN8	LT1178MJ8
LT1084CT	LT1115CN8	LT1126CS8	LT1178S
LT1085CM	LT1115CS	LT1127CN	LT1179ACJ
LT1085CT	LT1116CN8	LT1127CSW	LT1179ACN
LT1097CN8	LT1116CS8	LT1128CN8	LT1179AMJ
LT1097S8	LT1121CN8	LT1128CS8	LT1179CJ
LT1101ACH	LT1121CS8	LT1129CQ	LT1179CN
LT1101ACJ8	LT1122ACJ8	LT1129CS8	LT1179IN
LT1101ACN8	LT1122ACN8	LT1129CT	LT1179MJ

Multisim 14.0 Power Pro Components

LT1179S	LT1193CN8	LT1210CR	LT1217CS8
LT1179SW	LT1193CS8	LT1210CS	LT1218CN8
LT1187CJ8	LT1193MJ8	LT1210CT7	LT1218CS8
LT1187CN8	LT1194CJ8	LT1211ACN8	LT1219CN8
LT1187CS8	LT1194CN8	LT1211AMJ8	LT1219CS8
LT1187MJ8	LT1194CS8	LT1211CN8	LT1220CN8
LT1189CJ8	LT1194MJ8	LT1211CS8	LT1220CS8
LT1189CN8	LT1195CJ8	LT1211MJ8	LT1220MJ8
LT1189CS8	LT1195CN8	LT1212CN	LT1221CN8
LT1189MJ8	LT1195CS8	LT1212CS	LT1221CS8
LT118AH	LT1195MJ8	LT1213ACN8	LT1221MJ8
LT118AJ8	LT1200	LT1213AMJ8	LT1222CN8
LT1190CJ8	LT1201CN8	LT1213CN8	LT1222IS8
LT1190CN8	LT1201CS8	LT1213CS8	LT1223CJ8
LT1190CS8	LT1202CN	LT1213MJ8	LT1223CN8
LT1190MJ8	LT1202CS	LT1214CN	LT1223CS8
LT1191CJ8	LT1206CN8	LT1214CS	LT1223MJ8
LT1191CN8	LT1206CR	LT1215ACN8	LT1224CN8
LT1191CS8	LT1206CS8	LT1215AMJ8	LT1224CS8
LT1191MJ8	LT1206CY	LT1215CN8	LT1225CN8
LT1192CJ8	LT1207CS	LT1215CS8	LT1225CS8
LT1192CN8	LT1208CN8	LT1215MJ8	LT1226CN8
LT1192CS8	LT1208CS8	LT1216CN	LT1226CS8
LT1192MJ8	LT1209CN	LT1216CS	LT1227CN8
LT1193CJ8	LT1209CS	LT1217CN8	LT1227CS8

Multisim 14.0 Power Pro Components

LT1227MJ8	LT1260CS	LT1361CS8	LT1397CS
LT1228CN8	LT1328CMS8	LT1362CN	LT1398CS
LT1228CS8	LT1328CS8	LT1362CS	LT1399CGN
LT1229CJ8	LT1351CMS8	LT1363CN8	LT1399CS
LT1229CN8	LT1351CN8	LT1363CS8	LT1413ACN8
LT1229CS8	LT1351CS8	LT1364CN8	LT1413CN8
LT1229MJ8	LT1352CN8	LT1364CS8	LT1413S8
LT1230CJ	LT1352CS8	LT1365CN	LT1431CN8
LT1230CN	LT1353CS	LT1365CS	LT1431CS8
LT1230CS	LT1354CN8	LT1366CN8	LT1457CN8
LT1230MJ	LT1354CS8	LT1366CS8	LT1457S8
LT1236BIS8-5	LT1355CN8	LT1367CS	LT1461-25
LT1251CN	LT1355CS8	LT1368CN8	LT1461-3
LT1251CS	LT1356CN	LT1368CS8	LT1461-33
LT1252CN8	LT1356CS	LT1369CS	LT1461-4
LT1252CS8	LT1357CN8	LT1394CMS8	LT1461-5
LT1253CN8	LT1357CS8	LT1394CS8	LT1462CN8
LT1253CS8	LT1358CN8	LT1394IS8	LT1462CS8
LT1254CN	LT1358CS8	LT1395CS5	LT1463CN
LT1254CS	LT1359CN	LT1395CS6	LT1463CS
LT1256CN	LT1359CS	LT1395CS8	LT1464CN8
LT1256CS	LT1359CS14	LT1396CDD	LT1464CS8
LT1259CN	LT1360CN8	LT1396CMS8	LT1465CN
LT1259CS	LT1360CS8	LT1396CS8	LT1465CS
LT1260CN	LT1361CN8	LT1397CGN	LT1466LCN8

Multisim 14.0 Power Pro Components

LT1466LCS8	LT1497CS	LT1637CN8	LT1677CS8
LT1467LCS	LT1497CS8	LT1637CS8	LT1678CS8
LT1468CDD	LT1498CN8	LT1638CDD	LT1679CS
LT1468CN8	LT1498CS8	LT1638CMS8	LT1711CMS8
LT1468CS8	LT1499CS	LT1638CN8	LT1712CGN
LT1468IDD	LT1521CMS8	LT1638CS8	LT1713CMS8
LT1468IN8	LT1521CS8	LT1639CN	LT1714CGN
LT1468IS8	LT1529CQ	LT1639CS	LT1715CMS
LT1469CN8	LT1529CT	LT1671CMS8	LT1716CS5
LT1469CS8	LT1568CGN	LT1671CS8	LT1719CS8
LT1490CMS8	LT1568IGN	LT1672CMS8	LT1719IS8
LT1490CN8	LT1630CN8	LT1672CN8	LT1720CDD
LT1490CS8	LT1630CS8	LT1672CS8	LT1720CMS8
LT1491CN	LT1631CS	LT1672IMS8	LT1720CS8
LT1491CS	LT1632CN8	LT1672IN8	LT1720IDD
LT1492CN8	LT1632CS8	LT1672IS8	LT1720IMS8
LT1492CS8	LT1633CS	LT1673CN8	LT1720IS8
LT1493CS	LT1635CN8	LT1673CS8	LT1721CGN
LT1494CMS8	LT1635CS8	LT1673IN8	LT1721CS
LT1494CN8	LT1636CDD	LT1673IS8	LT1721IGN
LT1494CS8	LT1636CMS8	LT1674CN	LT1722CS5
LT1495CN8	LT1636CN8	LT1674CS	LT1722CS8
LT1495CS8	LT1636CS8	LT1674IN	LT1723CMS8
LT1496CN	LT1637CDD	LT1674IS	LT1723CS8
LT1496CS	LT1637CMS8	LT1677CN8	LT1724CS

Multisim 14.0 Power Pro Components

LT1739CFE	LT1763CS8-1.5	LT1789CS8-10	LT1807CMS8
LT1739CUE	LT1763CS8-1.8	LT1790ACS6-1.25	LT1807CS8
LT1739IFE	LT1763CS8-2.5	LT1790ACS6-2.048	LT1809CS6
LT1739IUE	LT1763CS8-3	LT1790ACS6-2.5	LT1809CS8
LT1761ES5-1.8	LT1763CS8-3.3	LT1790ACS6-3	LT1810CMS8
LT1761ES5-2	LT1763CS8-5	LT1790ACS6-3.3	LT1810CS8
LT1761ES5-2.5	LT1763IS8	LT1790ACS6-4.096	LT1812CS5
LT1761ES5-3	LT1763IS8-1.5	LT1790ACS6-5	LT1812CS6
LT1761ES5-3.3	LT1763IS8-1.8	LT1792CN8	LT1812CS8
LT1761ES5-5	LT1764EFE	LT1792CS8	LT1813CDD
LT1761ES5-BYP	LT1764EFE-1.5	LT1793CN8	LT1813CS8
LT1761ES5-SD	LT1764EFE-1.8	LT1793CS8	LT1813DMS8
LT1762EMS8	LT1764EFE-2.5	LT1794CFE	LT1814CGN
LT1762EMS8-2.5	LT1764EFE-3.3	LT1794CSW	LT1814CS
LT1762EMS8-3	LT1764EQ	LT1795CFE	LT1815CS5
LT1762EMS8-3.3	LT1764EQ-1.5	LT1795CSW	LT1815CS6
LT1762EMS8-5	LT1764EQ-1.8	LT1797CS5	LT1815CS8
LT1763CDE	LT1764EQ-2.5	LT1800CS5	LT1815IS5
LT1763CDE-1.5	LT1764EQ-3.3	LT1800CS8	LT1815IS6
LT1763CDE-1.8	LT1782CS6	LT1801CDD	LT1815IS8
LT1763CDE-2.5	LT1783CS6	LT1801CMS8	LT1816ACMS
LT1763CDE-3	LT1784CS6	LT1801CS8	LT1816AIMS
LT1763CDE-3.3	LT1784IS6	LT1802CS	LT1816CDD
LT1763CDE-5	LT1787CMS8	LT1806CS6	LT1816CMS8
LT1763CS8	LT1789CS8-1	LT1806CS8	LT1816CS8

Multisim 14.0 Power Pro Components

LT1816IDD	LT1962EMS8	LT1996CDD	LT6003CS5
LT1816IMS8	LT1962EMS8-1.5	LT1996CMS	LT6003HDC
LT1816IS8	LT1962EMS8-1.8	LT2078ACS8	LT6003HS5
LT1817CGN	LT1962EMS8-2.5	LT2078AIS8	LT6003IDC
LT1817CS	LT1962EMS8-3	LT2078CS8	LT6003IS5
LT1817IGN	LT1962EMS8-3.3	LT2079ACS	LT6004CDD
LT1817IS	LT1962EMS8-5	LT2079CS	LT6004CMS8
LT1818CS5	LT1963EFE	LT2178ACS8	LT6004HDD
LT1818CS8	LT1963EFE-1.5	LT2178CS8	LT6004HMS8
LT1818IS5	LT1963EFE-1.8	LT2179ACS	LT6004IDD
LT1818IS8	LT1963EFE-2.5	LT2179CS	LT6004IMS8
LT1819CMS8	LT1963EFE-3.3	LT318A	LT6005CDHC
LT1819CS8	LT1970CFE	LT318AJ8	LT6005CGN
LT1819IMS8	LT1990CS8	LT318AN8	LT6005HDHC
LT1819IS8	LT1991CDD	LT6000CDCB	LT6005HGN
LT1880CS5	LT1991CMS	LT6000IDCB	LT6005IDHC
LT1881CN8	LT1993CUD-10	LT6001CDD	LT6005IGN
LT1881CS8	LT1993CUD-2	LT6001CMS8	LT6010CDD
LT1882CS	LT1993CUD-4	LT6001IDD	LT6010CS8
LT1884CN8	LT1994CDD	LT6001IMS8	LT6011CDD
LT1884CS8	LT1994CMS8	LT6002CDHC	LT6011CMS8
LT1885CS	LT1995CDD	LT6002CGN	LT6011CS8
LT1886CS8	LT1995CMS	LT6002IDHC	LT6012CGN
LT1920CN8	LT1995IDD	LT6002IGN	LT6012CS
LT1920CS8	LT1995IMS	LT6003CDC	LT6100CDD

Multisim 14.0 Power Pro Components

LT6100CMS8	LT6231CDD	LT6557IGN	LTC1050ACJ8
LT6200CS6	LT6231CS8	LT6558CDHC	LTC1050ACN
LT6200CS6-10	LT6232CGN	LT6558CGN	LTC1050ACN8
LT6200CS6-5	LT6233CS6	LT6558IDHC	LTC1050AMH
LT6200CS8	LT6234CDD	LT6558IGN	LTC1050AMJ8
LT6200CS8-10	LT6234CS8	LT6559CUD	LTC1050CH
LT6200CS8-5	LT6235CGN	LT6600-10	LTC1050CJ8
LT6201CDD	LT6235IGN	LT6600-2.5	LTC1050CN
LT6201CS8	LT6402CUD-12	LT6600-20	LTC1050CN8
LT6202CS5	LT6402CUD-20	LT6600-5	LTC1050MH
LT6202CS8	LT6402CUD-6	LT6650CS5	LTC1050MJ8
LT6203CDD	LT6402IUD-12	LT6700CDCB-1	LTC1051ACJ8
LT6203CMS8	LT6402IUD-20	LT6700CDCB-2	LTC1051ACN8
LT6203CS8	LT6402IUD-6	LT6700CDCB-3	LTC1051ACS
LT6204CGN	LT6411CUD	LT6700CS6-1	LTC1051AMJ8
LT6204CS	LT6411IUD	LT6700CS6-2	LTC1051CJ8
LT6205CS5	LT6552CDD	LT6700CS6-3	LTC1051CN8
LT6206CMS8	LT6552CS8	LTC1043CN	LTC1051CS
LT6207CGN	LT6552IDD	LTC1043CSW	LTC1051MJ8
LT6220CS5	LT6552IS8	LTC1047CN8	LTC1052CD
LT6220CS8	LT6553CGN	LTC1047CS	LTC1052CP
LT6221CDD	LT6553IGN	LTC1049CJ8	LTC1052CS
LT6221CS8	LT6557CDHC	LTC1049CN8	LTC1052MD
LT6222CGN	LT6557CGN	LTC1049CS8	LTC1052MP
LT6230CS6	LT6557IDHC	LTC1050ACH	LTC1053CN

Multisim 14.0 Power Pro Components

LTC1053CS	LTC1444CDHD	LTC1798CS8-5	LTC6101BCS5
LTC1053CSW	LTC1444CN	LTC1841CS8	LTC6240CS5
LTC1100CN8	LTC1444CS	LTC1842CS8	LTC6240CS8
LTC1100CSW	LTC1444IDHD	LTC1966CMS8	LTC6240HS5
LTC1150CJ8	LTC1444IN	LTC1967CMS8	LTC6240HS8
LTC1150CN8	LTC1444IS	LTC1968CMS8	LTC6240IS5
LTC1150CS8	LTC1445CDHD	LTC2050CS5	LTC6240IS8
LTC1150MJ8	LTC1445CN	LTC2050CS6	LTC6241CDD
LTC1151CN8	LTC1445CS	LTC2050CS8	LTC6241CS8
LTC1151CSW	LTC152	LTC2051CMS10	LTC6241HS8
LTC1152CN8	LTC1540CDD	LTC2052CGN	LTC6241IDD
LTC1152CS8	LTC1540CMS8	LTC2052CS	LTC6241IS8
LTC1250CN8	LTC1540CS8	LTC2053CDD	LTC6242CDHC
LTC1250CS8	LTC1541CDD	LTC2053CMS8	LTC6242CGN
LTC1440CDD	LTC1541CMS8	LTC2053HDD	LTC6242HGN
LTC1440CMS8	LTC1541CS8	LTC2053HMS8	LTC6242IDHC
LTC1440CN8	LTC1542CDD	LTC2053IMS8-SYNC	LTC6242IGN
LTC1440CS8	LTC1542CMS8	LTC2054CS5	LTC6244CDD
LTC1441CN8	LTC1542CS8	LTC2055CDD	LTC6244CMS8
LTC1441CS8	LTC1563-2CGN	LTC2055CMS8	LTC6244HMS8
LTC1442CN8	LTC1563-3CGN	LTC6078CDD	LTC6244IDD
LTC1442CS8	LTC1798CS8	LTC6078CMS8	LTC6244IMS8
LTC1443CDHD	LTC1798CS8-2.5	LTC6079CDHC	LTC6800HDD
LTC1443CN	LTC1798CS8-3	LTC6079CGN	LTC6800HMS8
LTC1443CS	LTC1798CS8-4.1	LTC6101ACMS8	LTC6910-1CTS8

Multisim 14.0 Power Pro Components

LTC6910-2CTS8	M6060P-E3/45	MA344	MAC15-4
LTC6910-3CTS8	M68AF031AL_SO28	MA345	MAC15-6
LTC6911CMS-1	M68AF127BL_SO32	MA346	MAC15-8
LTC6911CMS-2	M68AF511AL_SO32	MA348	MAC15A-10
LTC7652CH	M68AW031AL_SO28	MA351	MAC15A-4
LTR-516AD	M68AW064FL_FBG A48	MA357	MAC15A-6
LVL_BARGRAPH	M68AW128ML_SO44	MA360	MAC15A-8
LVM_CURRENT	M68AW256ML_SO44	MA365	MAC210-10
LVM_VOLTAGE	M68AW511AL_SO32	MA366	MAC210-4
LVT22V10-7A	M68AW512DL_FBG A48	MA367	MAC210-6
LVT22V10-7N	M68AW512ML_SO44	MA368	MAC210-8
LVT22V10B7A	M68AW512ML_SO44	MA370	MAC210A-10
M37702S1AFP	MA321	MA371	MAC210A-4
M37702S1BFP	MA329	MA372	MAC210A-6
M51922L	MA331	MA372J	MAC210A-8
M51923FP	MA333	MA374	MAC212-10
M51923P	MA334	MA376	MAC212-4
M51924FP	MA335	MA377	MAC212-6
M51924P	MA337	MA391	MAC212-8
M5233FP	MA338	MA392	MAC212A-10
M5233L	MA339	MA393	MAC212A-4
M5233P	MA341	MA840	MAC212A-6
M5234FP		MAC08MT1G	MAC212A-8
M5234P		MAC12HCDG	MAC223-10
M5239L		MAC15-10	MAC223-4

Multisim 14.0 Power Pro Components

MAC223-6	MAGNETIC_CORE_	MAX1293_SO24	MAX15024DATB+T
MAC223-8	VIRTUAL	MAX1420_FP48	MAX15025CATB+T
MAC223A-4	MAT02EH	MAX1421_FP48	MAX16010TAA+
MAC223A-6	MAT02FH	MAX1422_FP48	MAX16010TAB+
MAC223A-8	MAT03EH	MAX1444_FP32	MAX16010TAC+
MAC224-10	MAT03FH	MAX1446_FP32	MAX1666VEEP
MAC224-4	MAT04AY	MAX1449_FP32	MAX1966_SO8
MAC224-6	MAT04EY	MAX14802ECM+	MAX1967_SO10
MAC224-8	MAT04FP	MAX14803AEWZ+	MAX200CPP
MAC224A-10	MAT04FS	MAX14803CCM+	MAX200ECWP
MAC224A-4	MAT04FY	MAX15000AEUB+	MAX200EEWP
MAC224A-6	MAX1180_FP48	MAX15000BEUB+	MAX200EPP
MAC224A-8	MAX1181_FP48	MAX15001AEUB+	MAX201CPD
MAC228-10	MAX1182_FP48	MAX15001BEUB+	MAX201CWE
MAC228-4	MAX1183_FP48	MAX15004AAUE+	MAX201EPD
MAC228-6	MAX1184_FP48	MAX15004BAUE+	MAX201EWE
MAC228-8	MAX1185_FP48	MAX15005AAUE+	MAX202CPE
MAC228A-10	MAX1195_FP48	MAX15005BAUE+	MAX202CSE
MAC228A-4	MAX1197_FP48	MAX15006AASA+	MAX202CWE
MAC228A-6	MAX1198_FP48	MAX15006AATT+	MAX202ECPE
MAC228A-8	MAX1284_SO8	MAX15007AASA+	MAX202ECUE
MAC23A-10	MAX1285_SO8	MAX15007AATT+	MAX202EEPE
MAG_CMP4	MAX1290_SO28	MAX15024AATB+	MAX202EEUE
MAG_OL	MAX1291_SO28	MAX15024BATB+	MAX202ESE
MAG_OL_RELAY	MAX1292_SO24	MAX15024CATB+	MAX202EWE

Multisim 14.0 Power Pro Components

MAX202SE	MAX207CAG	MAX213E	MAX253CPA+
MAX203CPP	MAX207E	MAX213EAI	MAX253CSA+
MAX203CWP	MAX207EAG	MAX213ECAI	MAX253CUA+
MAX203E	MAX207ECAG	MAX213ECWI	MAX253EPA+
MAX203ECPP	MAX207EEAG	MAX213EEAI	MAX253ESA+
MAX203ECWP	MAX208	MAX213EEWI	MAX253EUA+
MAX203EEPP	MAX208CAG	MAX218	MAX253MJA
MAX203EEWP	MAX208E	MAX218CAP	MAX253MSA/PR
MAX203EPP	MAX208EAG	MAX218CPP	MAX263_DIP28
MAX203EWP	MAX208ECAG	MAX218EAP	MAX264_DIP28
MAX204CPE	MAX208ECWG	MAX218EPP	MAX267_DIP24
MAX204CWE	MAX208EEAG	MAX221ECAE	MAX268_DIP24
MAX204EPE	MAX208EEWG	MAX221ECUE	MAX2740ECM
MAX204EWE	MAX209	MAX221EEAE	MAX274ACNG
MAX205CPG	MAX209ENG	MAX221EEUE	MAX274ACWI
MAX205E	MAX211	MAX222CPN	MAX274BCNG
MAX205ECAG	MAX211CAI	MAX222CWIN	MAX274BCWI
MAX205ECWG	MAX211E	MAX232E	MAX280_SO16
MAX205EEAG	MAX211EAI	MAX232ECPE	MAX281A_SO16
MAX205EEWG	MAX211ECAI	MAX232EEPE	MAX291_SO16
MAX206	MAX211ECWI	MAX241E	MAX292_SO16
MAX206CAG	MAX211EEAI	MAX241ECAI	MAX295_SO16
MAX206E	MAX211EEWI	MAX241ECWI	MAX296_SO16
MAX206EAG	MAX213	MAX241EEAI	MAX317CJA
MAX207	MAX213CAI	MAX241EEWI	MAX317CPA+

Multisim 14.0 Power Pro Components

MAX317CSA+	MAX3218EAP	MAX3243	MAX4024EUD+
MAX317EJA	MAX3218EPP	MAX3243E	MAX4027ESD+
MAX317EPA+	MAX3221	MAX3243ECAI	MAX4027EUD+
MAX317ESA+	MAX3221CAE	MAX3243ECAP	MAX4028EUE+
MAX317MJA	MAX3221E	MAX3243ECPP	MAX4028EWE+
MAX318CJA	MAX3221EAE	MAX3243EEAI	MAX4029EUP+
MAX318CPA+	MAX3221ECAE	MAX3243IDBR	MAX4029EWP+
MAX318CSA+	MAX3221EEAE	MAX3248E	MAX402CPA
MAX318EJA	MAX3222	MAX3380E	MAX402CSA
MAX318EPA	MAX3222E	MAX3381E	MAX402EPA
MAX318ESA+	MAX3223	MAX4004EUT+	MAX402ESA
MAX318MJA	MAX3223E	MAX4006EUT+	MAX4032EUT+
MAX319CJA	MAX3223ECAP	MAX4007EUT+	MAX4032EXT+
MAX319CPA+	MAX3223ECPP	MAX4008EUT+	MAX4036AAXK+
MAX319CSA+	MAX3223ECUP	MAX4012ESA+	MAX4036EXK+
MAX319EJA	MAX3223EEAP	MAX4012EUK+	MAX4037EUT+
MAX319EPA+	MAX3223EEPP	MAX4016ESA+	MAX4038AAUA+
MAX319ESA+	MAX3223EEUP	MAX4016EUA+	MAX4038EBL+T
MAX319MJA	MAX3232	MAX4018EEE+	MAX4038ETA+
MAX3212	MAX3232E	MAX4018ESD+	MAX4038EUA+
MAX3212CAI	MAX3237	MAX4020EEE+	MAX4039EBL+T
MAX3212EAI	MAX3237E	MAX4020ESD+	MAX4039ETB+T
MAX3218	MAX3238E	MAX4023EEE+	MAX4039EUB+
MAX3218CAP	MAX3241	MAX4023ESE+	MAX403CPA
MAX3218CPP	MAX3241E	MAX4024ESD+	MAX403CSA

Multisim 14.0 Power Pro Components

MAX403EPA	MAX407MJA	MAX409BCSA+	MAX410CPA
MAX403ESA	MAX4080FASA+	MAX409BEPA+	MAX410CPA+
MAX4069AUB+	MAX4080FAUA+	MAX409BESA+	MAX410CSA
MAX406ACPA+	MAX4080SASA+	MAX4100ESA	MAX410CSA+
MAX406ACSA+	MAX4080SAUA+	MAX4100ESA+	MAX410EPA
MAX406AEPA+	MAX4080TASA+	MAX4100EUA+	MAX410EPA+
MAX406AESA+	MAX4080TAUA+	MAX4101ESA	MAX410ESA+
MAX406AMJA	MAX4081FASA+	MAX4101ESA+	MAX410ETA-T
MAX406BCPA+	MAX4081FAUA+	MAX4104ESA	MAX4112ESA+
MAX406BCSA+	MAX4081SASA+	MAX4104ESA+	MAX4112EUA
MAX406BEPA+	MAX4081SAUA+	MAX4104EUK+	MAX4113ESA+
MAX406BESA+	MAX4081TASA+	MAX4105ESA+	MAX4117ESA+
MAX406BMJA	MAX4081TAUA+	MAX4105EUK+T	MAX4118ESA+
MAX4070ATA+	MAX4090AALT+T	MAX4106ESA	MAX4119EEE
MAX4070AUA+	MAX4090AAUT+	MAX4106ESA+	MAX4119ESD+
MAX4071ATA+	MAX4090AAXT+	MAX4107ESA	MAX4120ESD+
MAX4071AUA+	MAX4090ELT+T	MAX4107ESA+	MAX4122EUK+
MAX4072ATA+	MAX4090EUT+	MAX4108ESA	MAX4124EUK+
MAX4072AUA+	MAX4090EXT+	MAX4108ESA+	MAX4126ESA+
MAX4073TAUT+	MAX409ACPA+	MAX4109ESA+	MAX4126EUA+
MAX4073TAXK+	MAX409ACSA+	MAX410BCPA	MAX4128ESA+
MAX407CPA+	MAX409AEPA	MAX410BCSA	MAX4128EUA+
MAX407CSA+	MAX409AESA+	MAX410BCSA+	MAX4129ESD+
MAX407EPA+	MAX409AMJA	MAX410BEPA	MAX412BCPA
MAX407ESA+	MAX409BCPA+	MAX410BESA	MAX412BCPA+

Multisim 14.0 Power Pro Components

MAX412BCSA	MAX4145EEE+	MAX4163EUA+	MAX417ESA+
MAX412BCSA+	MAX4145ESD+	MAX4164ESD+	MAX417MJA
MAX412BEPA	MAX4146EEE+	MAX4165EUK+	MAX4180ESA+
MAX412BEPA+	MAX4146ESD+	MAX4166ELA+	MAX4180EUT+T
MAX412BESA	MAX4147ESD	MAX4166EPA+	MAX4181ESA+
MAX412BESA+	MAX4147ESD+	MAX4166ESA+	MAX4181EUT+T
MAX412CPA	MAX414BCPD	MAX4166EUA+	MAX4182ESA+
MAX412CPA+	MAX414BCSD	MAX4167EPA+	MAX4183ESD+
MAX412CSA	MAX414BCSD+	MAX4167ESA+	MAX4183EUB+
MAX412CSA+	MAX414BEPD	MAX4168EPD+	MAX4184ESA+
MAX412EPA	MAX414BESD	MAX4168ESD+	MAX4185ESD
MAX412EPA+	MAX414BESD+	MAX4168EUB+	MAX4185EUB+
MAX412ESA	MAX414CPD	MAX4169EPD	MAX4186ESD+
MAX412ESA+	MAX414CPD+	MAX4169ESD+	MAX4187EEE+
MAX412MJA	MAX414CSD	MAX4172EUA+	MAX4187ESD+
MAX4130EUK+	MAX414CSD+	MAX4173TESA+	MAX4188EEE+
MAX4131EBT+	MAX414EPD	MAX4173TEUT+	MAX4188ESD+
MAX4131ESA+	MAX414EPD+	MAX4178EPA+	MAX4189EEE+
MAX4131EUA+	MAX414ESD	MAX4178ESA+	MAX4189ESD+
MAX4132ESA+	MAX414ESD+	MAX4178EUA+	MAX418CPD+
MAX4132EUA+	MAX414MJD	MAX4178EUK+T	MAX418CSD+
MAX4133ESD	MAX4162ESA+	MAX4178MJA	MAX418EPD+
MAX4134ESD+	MAX4162EUK+	MAX417CPA+	MAX418ESD+
MAX4144EEE+	MAX4163EBL+	MAX417CSA+	MAX418MJD
MAX4144ESD+	MAX4163ESA+	MAX417EPA+	MAX4190ESA+

Multisim 14.0 Power Pro Components

MAX4190EUA	MAX4205EUA+	MAX4226ESD	MAX4237BEUA+
MAX4194ESA+	MAX4206ETE	MAX4226EUB+	MAX4237EUT+
MAX4195ESA+	MAX4212EUK+	MAX4227ESA+	MAX4238ASA+
MAX4196ESA+	MAX4213ESA+	MAX4228ESD+	MAX4238ATT+
MAX4197ESA+	MAX4213EUA+	MAX4228EUB+	MAX4238AUT+
MAX4198ESA+	MAX4214EUK+	MAX4230AUK+	MAX4239ASA+
MAX4198EUA+	MAX4215ESA+	MAX4230AXK+	MAX4239ATT+
MAX4199ESA+	MAX4215EUA+	MAX4231ART+T	MAX4239AUT+
MAX4199EUA+	MAX4216ESA+	MAX4231AUT+	MAX4240EUK+
MAX419CPD+	MAX4216EUA+	MAX4231AXT+	MAX4241ESA+
MAX419CSD+	MAX4217ESA+	MAX4231AYT+	MAX4241EUA+
MAX419EPD+	MAX4217EUA+	MAX4232AKA+	MAX4242ESA+
MAX419ESD+	MAX4218EEE+	MAX4232AUA+	MAX4242EUA+
MAX419MJD	MAX4218ESD+	MAX4233ABC+T	MAX4243ESD
MAX4200ESA+	MAX4219EEE+	MAX4233AUB+	MAX4243EUB+
MAX4200EUK+	MAX4219ESD+	MAX4234ASD+	MAX4244ESD+
MAX4201ESA+	MAX4220EEE+	MAX4234AUD+	MAX4245AUT+
MAX4201EUK+T	MAX4220ESD+	MAX4236AESA+	MAX4245AXT+
MAX4202ESA+	MAX4222EEE+	MAX4236AEUA	MAX4247AUB+
MAX4202EUK+T	MAX4222ESD+	MAX4236BESA+	MAX4249ESD+
MAX4203ESA+	MAX4223ESA+	MAX4236BEUA+	MAX4249EUB+
MAX4203EUA+	MAX4223EUT+	MAX4236EUT+	MAX4250AAUK+
MAX4204ESA+	MAX4224ESA+	MAX4237AESA+	MAX4250EUK+
MAX4204EUA+	MAX4224EUT+	MAX4237AEUA+	MAX4251ESA+
MAX4205ESA	MAX4225ESA+	MAX4237BESA+	MAX4251EUA+

Multisim 14.0 Power Pro Components

MAX4252EBL+	MAX4278ESA+	MAX4292EBL+	MAX4337EKA+
MAX4252ESA+	MAX4278EUA+	MAX4292ESA+	MAX4337EUA+
MAX4252EUA+	MAX4278EUK+	MAX4292EUA+	MAX4338EUB+
MAX4253EBC+	MAX4278MJA	MAX4294ESD+	MAX435CPD
MAX4253ESD+	MAX427CPA+	MAX4294EUD+	MAX435CSD
MAX4253EUB+	MAX427CSA+	MAX4304ESA+	MAX435CSD+
MAX4254ESD+	MAX427EPA+	MAX4304EUK+	MAX435EPD
MAX4255EUK+	MAX427ESA+	MAX4305ESA+	MAX435ESD
MAX4256ESA+	MAX427MJA	MAX4305EUK+	MAX435ESD+
MAX4256EUA+	MAX4281ESA+	MAX4323EBT+T	MAX435MJD
MAX4257ESA+	MAX4281EUK+	MAX4323ESA+	MAX4361
MAX4257EUA+	MAX4282ESA+	MAX4323EUA	MAX4361_SO8
MAX4265ESA+	MAX4282EUA+	MAX4323EUT+	MAX4361ESA
MAX4265EUA+	MAX4284EEE	MAX4327ESD	MAX4361EUA
MAX4266ESA+	MAX4284ESD	MAX4327EUB+	MAX4362ESD+
MAX4266EUA+	MAX4285ESA+	MAX4330EUK+	MAX4362EUB+
MAX4267ESA+	MAX4285EUT+	MAX4331ESA+	MAX4363EUP+
MAX4267EUA	MAX4286ESA+	MAX4331EUA+	MAX436CPD
MAX4268EEE+	MAX4286EUT-T	MAX4332ESA+	MAX436CSD
MAX4268ESD+	MAX4288ESD	MAX4333ESD+	MAX436CSD+
MAX4269EEE	MAX4288EUB	MAX4333EUB+	MAX436EPD
MAX4269ESD	MAX4289ESA+	MAX4334ESD+	MAX436ESD
MAX4270EEE	MAX4289EUT+	MAX4335EXT+	MAX436ESD+
MAX4270ESD	MAX4291EUK+	MAX4336EUT-T	MAX436MJD
MAX4278EPA+	MAX4291EXK+	MAX4336EXT+	MAX4372FEBT+T

Multisim 14.0 Power Pro Components

MAX4372FESA+	MAX4375TEUB+	MAX4390EXT+	MAX4416EUA+
MAX4372FEUK+	MAX437CPA	MAX4392ESA+	MAX4417ESA+
MAX4372HEBT+T	MAX437CSA+	MAX4392EUA+	MAX4417EUA+
MAX4372HESA+	MAX437EPA	MAX4393EUB+	MAX4418EUD+
MAX4372HEUK+	MAX437ESA+	MAX4394ESD+	MAX4419EUD+
MAX4372TEBT+T	MAX437MJA	MAX4394EUD+	MAX44241AUA+
MAX4372TESA+	MAX4380EUT+	MAX4395ESD+	MAX44241AUK+T
MAX4372TEUK+	MAX4380EXT+	MAX4395EUD+	MAX44243ASD+
MAX4373FESA+	MAX4381EUB+	MAX4396EUP+	MAX44243AUD+
MAX4373FEUA+	MAX4382EEE+	MAX4400AUK+	MAX44251AKA+
MAX4373HESA+	MAX4382ESD+	MAX4400AXK+	MAX44251AUA+
MAX4373HEUA+	MAX4382EUD+	MAX4401AXT+	MAX44252ASD+
MAX4373TESA+	MAX4383EEE+	MAX4402AKA+	MAX44264EWT+
MAX4373TEUA+	MAX4383ESD+	MAX4402ASA+	MAX44265EWT+
MAX4374FESD+	MAX4383ESE+	MAX4402AUA+	MAX44269EWL+
MAX4374FEUB+	MAX4383EUD+	MAX4403ASD+	MAX44280AXT+
MAX4374HESD+	MAX4384EUP+	MAX4403AUD+	MAX44280AYT+
MAX4374HEUB+	MAX4385EEUK+	MAX4412EUK+	MAX44281OANS+
MAX4374TESD+	MAX4386EESD+	MAX4412EXK+	MAX44281UANS+
MAX4374TEUB+	MAX4386EEUD+	MAX4413EKA+	MAX44281VANS+
MAX4375FESD+	MAX4388ESD+	MAX4414ESA+	MAX44285FAUA+
MAX4375FEUB+	MAX4388EUB	MAX4414EUA+	MAX44285FAWA+T
MAX4375HESD+	MAX4389EUT+	MAX4415ESA+	MAX44285HAUA+
MAX4375HEUB+	MAX4389EXT+	MAX4415EUA+	MAX44285HAWA+T
MAX4375TESD+	MAX4390EUK+	MAX4416ESA+	MAX44285LAUA+

Multisim 14.0 Power Pro Components

MAX44285LAWA+T	MAX4454EUD+	MAX4474EKA+	MAX4486ASA+
MAX44285TAUA+	MAX4460ESA+	MAX4474ESA+	MAX4486AUA+
MAX44285TAWA+T	MAX4460ETT+	MAX4474EUA+	MAX4487ASD+
MAX4430ESA+	MAX4460EUT+T	MAX4475ASA+	MAX4487AUD+
MAX4430EUK+	MAX4461HESA+	MAX4475ATT+	MAX4488ASA+
MAX4432ESA	MAX4461HETT+T	MAX4475AUA+	MAX4488ATT+
MAX4432EUA+	MAX4461HEUT+	MAX4475AUT+	MAX4488AUA+
MAX4434ESA	MAX4461TESA+	MAX4476ATT+T	MAX4488AUT+
MAX4434EUK+	MAX4461TETT+	MAX4476AUT+	MAX4489ASA+
MAX4435ESA	MAX4461TEUT	MAX4477ASA+	MAX4489AUA+
MAX4435EUK	MAX4461UESA+	MAX4477AUA+	MAX4490AUK+T
MAX4436ESA	MAX4461UETT+T	MAX4478ASD+	MAX4490AXK+
MAX4436EUA+	MAX4461UEUT-T	MAX4478AUD+	MAX4491AKA+
MAX4437ESA	MAX4462HESA+	MAX4480AUK+	MAX4491AUA+
MAX4437EUA+	MAX4462HETT+	MAX4480AXK+	MAX4492ASD+
MAX4444ESE+	MAX4462HEUT+	MAX4481AUT+	MAX4492AUD+
MAX4450EUK+	MAX4462TESA	MAX4481AXT+	MAX4493AUK
MAX4450EXK+	MAX4462TETT+T	MAX4482AKA+	MAX4493AXK+
MAX4451EKA+	MAX4462TEUT	MAX4482ASA+	MAX4494AKA+
MAX4451ESA+	MAX4462UESA	MAX4482AUA+	MAX4494ASA+
MAX4452EUK+	MAX4462UETT+	MAX4483ASD+	MAX4494AUA+
MAX4452EXK+	MAX4464EUK+	MAX4483AUD+	MAX4495ASD+
MAX4453EKA+	MAX4464EXK+	MAX4484AUK+	MAX4495AUD+
MAX4453ESA+	MAX4473ESA	MAX4484AXK+	MAX4541CPA+
MAX4454ESD+	MAX4473EUA+	MAX4486AKA+	MAX4541CSA+

Multisim 14.0 Power Pro Components

MAX4541CUA+	MAX4601EWE	MAX4669CPE	MAX473CUA+
MAX4541EKA+	MAX4602CAE+	MAX4669CSE+	MAX473EPA+
MAX4541EPA	MAX4602CPE+	MAX4669EPE	MAX473ESA+
MAX4541ESA+	MAX4602CWE+	MAX4669ESE+	MAX473MJA
MAX4541ETA+T	MAX4602EAE+	MAX4670ETJ+	MAX474CPA
MAX4541EUA	MAX4602EPE	MAX4684EBC+	MAX474CPA+
MAX4541EUA+	MAX4602EWE+	MAX4684ETB+	MAX474CSA
MAX4542CSA+	MAX4603CAE+	MAX4684EUB+	MAX474CSA+
MAX4542CUA	MAX4603CPE+	MAX4685EBC+T	MAX474CUA
MAX4542EKA+	MAX4603CWE+	MAX4685ETB+T	MAX474CUA+
MAX4542EPA	MAX4603EAE+	MAX4685EUB+	MAX474EPA+
MAX4542ESA+	MAX4603EPE+	MAX4714ELT+	MAX474ESA+
MAX4542EUA+	MAX4603EWE+	MAX4714EXT+	MAX474MJA
MAX4543CPA	MAX4659ESA+	MAX4717EBC+	MAX4754AEBE+T
MAX4543CSA	MAX4659EUA+	MAX4717ETB+	MAX4754AETE+
MAX4543CUA	MAX4660ESA+	MAX4717EUB+	MAX4754EBE+T
MAX4543EKA+	MAX4660EUA+	MAX4718EBC-T	MAX4754ETE+
MAX4543EPA	MAX4667CPE	MAX4718EUB	MAX475CPD
MAX4543ESA+	MAX4667CSE	MAX4719EBC-T	MAX475CSD
MAX4543EUA+	MAX4667EPE	MAX4719EUB+	MAX475EPD
MAX4601CAE+	MAX4667ESE+	MAX473CPA	MAX475ESD
MAX4601CPE+	MAX4668CPE+	MAX473CPA+	MAX475MJD
MAX4601CWE+	MAX4668CSE+	MAX473CSA	MAX477EPA+
MAX4601EAE+	MAX4668EPE+	MAX473CSA+	MAX477ESA+
MAX4601EPE+	MAX4668ESE+	MAX473CUA	MAX477EUA+

Multisim 14.0 Power Pro Components

MAX477EUK+T	MAX4892ETX+	MAX495CUA+	MAX5631_QFN68
MAX477MJA	MAX4906FELB+	MAX495EPA+	MAX5632_QFN68
MAX478ACPA+	MAX4906FETB+T	MAX495ESA+	MAX5633_QFN68
MAX478CPA+	MAX4907FELA+	MAX495MJA	MAX5902AAETT+
MAX478CSA+	MAX4907FETA+T	MAX496CPE+	MAX5902AAEUT+
MAX478EPA+	MAX492CPA	MAX496CSE+	MAX5902ABETT+T
MAX478ESA+	MAX492CPA+	MAX497CPE+	MAX5902ABEUT+
MAX479ACPD	MAX492CSA	MAX497CSE+	MAX5902ABEUT-T
MAX479CPD+	MAX492CSA+	MAX5025EUT+	MAX5902ACETT+T
MAX479CSD+	MAX492EPA+	MAX5027EUT+	MAX5902ACEUT+
MAX479EPD+	MAX492ESA+	MAX5035AASA+	MAX5902LAETT+
MAX479ESD+	MAX492MJA	MAX5035AUPA+	MAX5902LAEUT+
MAX4800CCM+	MAX494CPD	MAX5035AUSA+	MAX5902LBETT+T
MAX4800CQI+	MAX494CPD+	MAX5035BASA+	MAX5902LBEUT+T
MAX4800CTM+	MAX494CSD	MAX5035BUPA+	MAX5902LCETT+T
MAX4800CXZ+	MAX494CSD+	MAX5035BUSA+	MAX5902LCEUT+
MAX4801CQI+	MAX494EPD+	MAX5035CASA+	MAX5903AAETT+T
MAX4818ETE+	MAX494ESD+	MAX5035CUPA+	MAX5903AAEUT+
MAX4819ETE	MAX494MJD	MAX5035CUSA+	MAX5903ABETT+
MAX4885EETG+	MAX4951CTP+	MAX5048AATT+	MAX5903ABEUT+
MAX4885ETJ+	MAX495CPA	MAX5048AAUT+T	MAX5903ACETT+
MAX4887ETE+	MAX495CPA+	MAX5054AATA+	MAX5903ACEUT+
MAX4889AETO+	MAX495CSA	MAX5064AATC+	MAX5903LAETT+T
MAX4890ETJ+	MAX495CSA+	MAX5078AATT+	MAX5903LAEUT+
MAX4891ETJ+	MAX495CUA	MAX5078BATT+	MAX5903LBETT+

Multisim 14.0 Power Pro Components

MAX5903LBEUT+	MAX6324BUT31-T	MAX6324FUT44-T	MAX706REPA
MAX5903LCETT+T	MAX6324BUT44-T	MAX6324FUT46+T	MAX706RESA+
MAX5903LCEUT+	MAX6324BUT46+T	MAX6324GUT23-T	MAX706REUA+
MAX5920AESA+	MAX6324CUT23+T	MAX6324GUT26+T	MAX706RMJA
MAX5920BESA+	MAX6324CUT26+T	MAX6324GUT29+T	MAX706TCPA+
MAX5921AESA+	MAX6324CUT29-T	MAX6324GUT31-T	MAX706TCSA+
MAX5941ACSE+	MAX6324CUT31-T	MAX6324GUT44-T	MAX706TCUA+
MAX5941AESE+	MAX6324CUT44-T	MAX6324GUT46+T	MAX706TEPA
MAX5941BCSE+	MAX6324CUT46+T	MAX6324HUT23+T	MAX706TESA+
MAX5941BESE+	MAX6324DUT23+T	MAX6324HUT26-T	MAX706TEUA+
MAX5942ACSE+	MAX6324DUT26+T	MAX6324HUT29+T	MAX706TMJA
MAX5942AESE+	MAX6324DUT29-T	MAX6324HUT31+T	MAX7400_DIP8
MAX5942BCSE+	MAX6324DUT31-T	MAX6324HUT44+T	MAX7401_DIP8
MAX5942BESE+	MAX6324DUT44-T	MAX6324HUT46+T	MAX7403_DIP8
MAX5949AESA+	MAX6324DUT46-T	MAX6460UT+	MAX7404_DIP8
MAX5953DUTM+	MAX6324EUT23+T	MAX6780LTA+	MAX7405_DIP8
MAX6324AUT23-T	MAX6324EUT26+T	MAX6817EUT/GH9-T	MAX7407_DIP8
MAX6324AUT26-T	MAX6324EUT29+	MAX6817EUT+	MAX7408_SO8
MAX6324AUT29+T	MAX6324EUT31-T	MAX6817EUT+T	MAX7409_SO8
MAX6324AUT31+T	MAX6324EUT44-T	MAX6817EUT-T	MAX7410_SO8
MAX6324AUT44-T	MAX6324EUT46+T	MAX6817EUT-TG1K	MAX7411_SO8
MAX6324AUT46+T	MAX6324FUT23+T	MAX706RCPA	MAX7412_SO8
MAX6324BUT23+T	MAX6324FUT26+T	MAX706RCSA+	MAX7413_SO8
MAX6324BUT26-T	MAX6324FUT29-T	MAX706RCUA+	MAX7414_SO8
MAX6324BUT29+T	MAX6324FUT31-T		MAX7415_SO8

Multisim 14.0 Power Pro Components

MAX7418_SO8	MAX809TEUR+	MAX9012ESA+	MAX907CSA
MAX7419_SO8	MAX809TEXR+	MAX9012EUA+	MAX907CSA+
MAX7420_SO8	MAX809ZEXR+	MAX9013ESA+	MAX907EPA
MAX7421_SO8	MAX810LEUR+	MAX9013EUA+	MAX907EPA+
MAX7422_SO8	MAX810LEXR+	MAX9015AEKA+	MAX907ESA
MAX7423_SO8	MAX810MEUR+	MAX9026EBT+	MAX907ESA+
MAX7424_SO8	MAX810MEXR+	MAX9030AUT+	MAX907MJA
MAX7425_SO8	MAX810REUR+	MAX9030AXT+	MAX908CPD
MAX7426_SO8	MAX810REXR+T	MAX9031AUK+	MAX908CPD+
MAX7427_SO8	MAX810SEUR+	MAX9031AXK+	MAX908CSD
MAX803LEXR+	MAX810SEXR+	MAX9032AKA+	MAX908CSD+
MAX803MEXR+	MAX810TEUR+	MAX9032ASA+	MAX908EPD
MAX803REXR+	MAX810TEXR+	MAX9032AUA+	MAX908EPD+
MAX803SEXR+	MAX810ZEXR+T	MAX9034ASD+	MAX908ESD
MAX803TEXR+	MAX8815AETB+	MAX9034AUD+	MAX908ESD+
MAX803ZEXR+	MAX9000ESA+	MAX9038BABT+T	MAX908MJD
MAX809JEUR+	MAX9000EUA+	MAX9038BEBT+T	MAX9092AKA+T
MAX809LEUR+	MAX9002ESA+	MAX9075EUK+	MAX9092AUA+
MAX809LEXR+	MAX9002EUA+	MAX9075EXK+	MAX9094ASD+
MAX809MEUR+	MAX9003ESA+	MAX9077EKA+	MAX9094AUD+
MAX809MEXR+	MAX9003EUA+	MAX9077ESA+	MAX909CPA
MAX809REUR+	MAX9005ESA+	MAX9077EUA+	MAX909CSA
MAX809REXR+	MAX9005EUA+	MAX9077MSA/PR2	MAX909EPA
MAX809SEUR+	MAX9010EXT+	MAX907CPA	MAX909ESA
MAX809SEXR+	MAX9011EUT+	MAX907CPA+	MAX909MJA

Multisim 14.0 Power Pro Components

MAX9117ESA+	MAX9140AAUK+	MAX921ESA+	MAX924CSE
MAX9117EXK+	MAX9140AAXK+	MAX921MJA	MAX924CSE+
MAX9119EXK+	MAX9140EUK+	MAX922CPA	MAX924EPE
MAX9120ESA	MAX9140EXK+	MAX922CPA+	MAX924EPE+
MAX9120EXK+	MAX9141EKA+	MAX922CSA	MAX924ESE
MAX912CPE	MAX9141ESA+	MAX922CSA+	MAX924ESE+
MAX912CPE+	MAX9142EKA+	MAX922CUA+	MAX924MJE
MAX912CSE	MAX9142ESA+	MAX922EPA	MAX931CPA
MAX912CSE+	MAX9144ESD+	MAX922EPA+	MAX931CSA
MAX912EPE	MAX9144EUD+	MAX922ESA	MAX931EPA
MAX912EPE+	MAX9201ESE+	MAX922ESA+	MAX931ESA
MAX912ESE	MAX9201EUE+	MAX922MJA	MAX932CPA
MAX912ESE+	MAX9202ESD+	MAX923CPA	MAX932CPA+
MAX912MJE	MAX9202EUD+	MAX923CPA+	MAX932CSA
MAX913CPA	MAX9203EKA+	MAX923CSA	MAX932CSA+
MAX913CPA+	MAX9203ESA+	MAX923CSA+	MAX932CUA+
MAX913CSA	MAX921CPA	MAX923CUA	MAX932EPA
MAX913CSA+	MAX921CPA+	MAX923CUA+	MAX932EPA+
MAX913EPA	MAX921CSA	MAX923EPA	MAX932ESA
MAX913EPA+	MAX921CSA+	MAX923EPA+	MAX932ESA+
MAX913ESA	MAX921CUA	MAX923ESA	MAX933CPA
MAX913ESA+	MAX921CUA+	MAX923ESA+	MAX933CPA+
MAX913EUA+	MAX921EPA	MAX923MJA	MAX933CSA
MAX913MJA	MAX921EPA+	MAX924CPE	MAX933CSA+
MAX913MSA/PR	MAX921ESA	MAX924CPE+	MAX933CUA+

Multisim 14.0 Power Pro Components

MAX933EPA	MAX942CPA+	MAX952EPA	MAX9552EUD+
MAX933EPA+	MAX942CSA	MAX952EPA+	MAX9600EUP+
MAX933ESA	MAX942CSA+	MAX952ESA	MAX9601EUP+
MAX933ESA+	MAX942CUA+	MAX952ESA+	MAX9602EUG+
MAX934CPE	MAX942EPA	MAX952EUA+	MAX9617AXT+
MAX934CPE+	MAX942EPA+	MAX952MJA	MAX9618AXA+
MAX934CSE	MAX942ESA	MAX953CPA	MAX9619AXT+
MAX934CSE+	MAX942ESA+	MAX953CSA	MAX961ESA
MAX934EPE	MAX942EUA+	MAX953EPA	MAX961ESA+
MAX934EPE+	MAX942MJA	MAX953EPA+	MAX961EUA+
MAX934ESE	MAX944CPD	MAX953ESA	MAX9620AXK+
MAX934ESE+	MAX944CPD+	MAX953ESA+	MAX9621AUB/V+
MAX941CPA	MAX944CSD	MAX953EUA+	MAX9621AUB/V+T
MAX941CPA+	MAX944CSD+	MAX953MJA	MAX9621AUB+
MAX941CSA	MAX944EPD	MAX954CPA	MAX9621AUB+T
MAX941CSA+	MAX944EPD+	MAX954CSA	MAX962ESA
MAX941CUA	MAX944ESD	MAX954EPA	MAX9636AXT+
MAX941EPA	MAX944ESD+	MAX954EPA+	MAX9637AXA+
MAX941EPA+	MAX944MJD	MAX954ESA	MAX9638AVB+
MAX941ESA	MAX951EPA+	MAX954ESA+	MAX963ESA
MAX941ESA+	MAX951ESA+	MAX954EUA+	MAX963ESD+
MAX941EUA+	MAX951EUA+	MAX954MJA	MAX9643TATA+T
MAX941MJA	MAX951MJA	MAX9550EUA+	MAX9643UATA+T
MAX942AUA+	MAX952CPA	MAX9550EZK+	MAX9647AUK+T
MAX942CPA	MAX952CSA	MAX9551EUA+	MAX9647AXK+T

Multisim 14.0 Power Pro Components

MAX964ESA	MAX978ESE+	MAX9915EXT+	MAX992EUA+
MAX9650ATA+	MAX985EBT+T	MAX9916EKA+	MAX9934FART+
MAX9650AUA+	MAX985ESA+	MAX9917EUB+	MAX9934FAUA+
MAX9650AZK+	MAX985EUK+	MAX9918ASA+	MAX9934TART+
MAX9651ATA+	MAX985EXK+	MAX9919FASA+	MAX9934TAUA+
MAX9651AUA+	MAX986ESA+	MAX9919NASA+	MAX993ESD+
MAX965ESA+	MAX986EUK+	MAX991EKA+	MAX993EUD+
MAX965EUA+	MAX986EXK+	MAX991ESA+	MAX9940AXK+
MAX9691EPA+	MAX987ESA+	MAX991EUA+	MAX9943ATT+T
MAX9691ESA+	MAX987EUK+	MAX9920ASA+	MAX9943AUA+
MAX9691EUA+	MAX987EXK+	MAX9924UAUB/V+	MAX9944ASA+
MAX9692EPE+	MAX988ESA+	MAX9924UAUB/V+ T	MAX9944ATA+T
MAX9692ESE+	MAX988EUK+	MAX9924UAUB+	MAX994ESD+
MAX9692EUB+	MAX988EXK+	MAX9924UAUB+T	MAX994EUD+
MAX9693EEE+	MAX989EKA+	MAX9926UAEE/V+	MAX995ESD+
MAX9693EPE+	MAX989ESA+	MAX9926UAEE/V+T	MAX995EUD+
MAX9693ESE+	MAX989EUA+	MAX9926UAEE+	MAX996ESD+
MAX975ESA+	MAX990EKA+	MAX9926UAEE+T	MAX996EUD+
MAX975EUA+	MAX990ESA+	MAX9928FABT+	MAX997ESA+
MAX976ESA+	MAX990EUA+	MAX9928FAUA+	MAX997EUA+
MAX976EUA+	MAX9910EXK+	MAX9929FABT+	MAX998ESA+
MAX976MUA/PR2	MAX9911EWT+	MAX9929FAUA+	MAX998EUT+
MAX977EEE+	MAX9911EXT+	MAX992EKA+	MAX999AAUK+5
MAX977ESD+	MAX9912EKA+	MAX992ESA+	MAX999EUK+
MAX978EEE+	MAX9913EUB+		MAXIM-MAXQ-HDR

Multisim 14.0 Power Pro Components

MB6S-E3/80	MBR1035G	MBR1240MFST3G	MBR1645G
MBD1057-C18	MBR1045	MBR130LSFT1G	MBR16H45-E3/45
MBD2057-C18	MBR1045G	MBR130T1	MBR1H100SFT3G
MBD3057-C18	MBR1045MFST1G	MBR130T1G	MBR20035CT
MBD4057-C18	MBR1045MFST3G	MBR130T3G	MBR20045CT
MBD5057-C18	MBR1060	MBR140ESFT1G	MBR20100
MBD770DWT1G	MBR1060G	MBR140ESFT3G	MBR20100CTG
MBR030	MBR1080G	MBR140SFT1G	MBR20100CTH
MBR040	MBR1090G	MBR140SFT3G	MBR20200CTG
MBR0520L	MBR10H100CTG	MBR150G	MBR2030CTLG
MBR0520LT1	MBR10H100CTHE3/45	MBR150RLG	MBR2035CT
MBR0520LT1G	MBR10H100-E3/45	MBR1520	MBR2045CT
MBR0520LT3G	MBR10L60CTG	MBR1530	MBR2045CTG
MBR0530	MBR1100G	MBR1535CT	MBR2045EMFST1G
MBR0530T1	MBR1100RLG	MBR1535CTG	MBR2045EMFST3G
MBR0530T1G	MBR12035CT	MBR1540	MBR2045MFST1G
MBR0530T3G	MBR12045CT	MBR1545CT	MBR2045MFST3G
MBR0540T1	MBR120ESFT1G	MBR1545CT-E3/45	MBR2060CTG
MBR0540T1G	MBR120ESFT3G	MBR1545CTG	MBR2080CTG
MBR0540T3G	MBR120LSFT1G	MBR160G	MBR2090CTG
MBR10100	MBR120LSFT3G	MBR160RLG	MBR20H100CT/45
MBR10100G	MBR120VLSFT1G	MBR16100CTG	MBR20H100CTG
MBR10100MFST1G	MBR120VLSFT3G	MBR1635	MBR20H150CTG
MBR10100MFST3G	MBR1240MFST1G	MBR1635G	MBR20H200CT-E3/45
MBR1035		MBR1645	

Multisim 14.0 Power Pro Components

MBR20L45CTG	MBR30H100MFST1G	MBR360RLG	MBR560MFST1G
MBR20L60CTG	MBR30H100MFST3G	MBR4015CTLG	MBR560MFST3G
MBR230LSFT1G	MBR30H150CTG	MBR4015LWT	MBR5825
MBR2520	MBR30H30CTG	MBR4015LWTG	MBR5825H
MBR2530	MBR30H60CTG	MBR4020	MBR5831
MBR2535CT	MBR30L45CTG	MBR40250G	MBR5831H
MBR2535CTG	MBR30L60CTG	MBR40250TG	MBR5H100MFST1G
MBR2535CTL	MBR3100G	MBR4030	MBR6035
MBR2535CTLG	MBR3100RLG	MBR4040	MBR6035B
MBR2540	MBR320M	MBR4045PT-E3/45	MBR6035PF
MBR2545CT	MBR320P	MBR4045PTG	MBR6045
MBR2545CTG	MBR330M	MBR4045WTG	MBR6045B
MBR2H100SFT3G	MBR330P	MBR4060PT-E3/45	MBR6045H
MBR30035CT	MBR340	MBR40H100WTG	MBR6045PF
MBR30045CT	MBR340G	MBR40L45CTG	MBR6045PTG
MBR3020CT	MBR340M	MBR40L60CTG	MBR6045WTG
MBR3035CT	MBR340P	MBR41H100CTG	MBR60H100CTG
MBR3035PT	MBR340RLG	MBR440MFST1G	MBR60L45CTG
MBR3045CT	MBR350RLG	MBR440MFST3G	MBR60L45WTG
MBR3045PT	MBR3520	MBR460MFST1G	MBR6535
MBR3045PTG	MBR3535	MBR460MFST3G	MBR6545
MBR3045STG	MBR3545	MBR5100MFST1G	MBR7030WTL
MBR3045WTG	MBR3545H	MBR5100MFST3G	MBR735
MBR30H100CTG	MBR360G	MBR540MFST1G	MBR735G
		MBR540MFST3G	MBR745

Multisim 14.0 Power Pro Components

MBR745-E3/45	MBRA340T3G	MBRB2535CTLT4G	MBRD320RLG
MBR745G	MBRAF1100T3G	MBRB2545CTG	MBRD320T4G
MBR7520	MBRAF1540T3G	MBRB2545CTT4G	MBRD330G
MBR7530	MBRAF2H100T3G	MBRB3030CT	MBRD330RLG
MBR7535	MBRAF3200T3G	MBRB3030CTG	MBRD330T4G
MBR7540	MBRAF440T3G	MBRB3030CTL	MBRD340G
MBR7545	MBRB1045G	MBRB3030CTLG	MBRD340RLG
MBR760-E3/45	MBRB1045T4G	MBRB3030CTT4G	MBRD340T4G
MBR7H45-E3/45	MBRB1545CTG	MBRB3045CT-1G	MBRD350G
MBR8035	MBRB1545CTT4	MBRB30H30CT-1G	MBRD350RLG
MBR8045	MBRB1545CTT4G	MBRB30H60CT-1G	MBRD350T4G
MBR8H100MFST1G	MBRB1645T4G	MBRB30H60CTT4G	MBRD360G
MBR8H100MFST3G	MBRB20100CTG	MBRB4030	MBRD360RLG
MBRA120ET3G	MBRB20100CTT4	MBRB4030G	MBRD360T4
MBRA130LT3	MBRB20100CTT4G	MBRB4030T4G	MBRD360T4G
MBRA130LT3G	MBRB20200CTG	MBRB41H100CT-1G	MBRD5H100T4G
MBRA140T3	MBRB20200CTT4	MBRB41H100CTT4	MBRD620CTT4G
MBRA140T3G	MBRB20200CTT4G	G	MBRD630CTT4G
MBRA160T3	MBRB2060CTG	MBRB60H100CTT4	MBRD640CTT4
MBRA160T3G	MBRB2060CTT4G	G	MBRD640CTT4G
MBRA1H100T3G	MBRB20H100CTT4	MBRB8H100T4G	MBRD650CTG
MBRA210ET3G	G	MBRD1035CTL	MBRD650CTT4G
MBRA210LT3G	MBRB2515LG	MBRD1035CTLG	MBRD660CTG
MBRA2H100T3G	MBRB2515LT4G	MBRD1035CTLT4G	MBRD660CTRLG
MBRA320T3G	MBRB2535CTLG	MBRD1045T4G	MBRD660CTT4G
		MBRD320G	

Multisim 14.0 Power Pro Components

MBRD835L	MBRM110LT1G	MBRS140T3G	MBRS410LT3G
MBRD835LG	MBRM110LT3G	MBRS1540T3G	MBRS4201T3G
MBRD835LT4G	MBRM120ET1G	MBRS190T3	MBRS540T3
MBRF10H150CTG	MBRM120ET3G	MBRS190T3G	MBRS540T3G
MBRF10L60CTG	MBRM120LT1	MBRS2040LT3	MBT2222ADW1T1G
MBRF20100CTG	MBRM120LT1G	MBRS2040LT3G	MBT35200MT1
MBRF20200CTG	MBRM120LT3	MBRS230LT3G	MBT35200MT1G
MBRF2045CTG	MBRM120LT3G	MBRS240LT3	MBT3904DW1T1G
MBRF2060CTG	MBRM130LT1G	MBRS240LT3G	MBT3946DW1T1G
MBRF20H100CTG	MBRM130LT3	MBRS260T3G	MBT3946DW1T2G
MBRF20H150CTG	MBRM130LT3G	MBRS2H100T3G	MC14016BCL
MBRF20L45CTG	MBRM140T1	MBRS3100T3G	MC14016BCP
MBRF20L60CTG	MBRM140T1G	MBRS3200T3	MC14016BD
MBRF20L80CTG	MBRM140T3	MBRS3200T3G	MC1403D
MBRF2545CTG	MBRM140T3G	MBRS3201T3G	MC1403U
MBRF30H100CTG	MBRM1H100T3G	MBRS320T3	MC1404P10
MBRF30H150CTG	MBRM2H100T3G	MBRS320T3G	MC1404P5
MBRF30H60CTG	MBRS1100T3	MBRS330T3G	MC1404P6
MBRF30L45CTG	MBRS1100T3G	MBRS340T3	MC1436CD
MBRF30L60CTG	MBRS120T3	MBRS340T3G	MC1436CG
MBRF40250TG	MBRS120T3G	MBRS360BT3G	MC1436CP1
MBRL030	MBRS130LT3	MBRS360T3	MC1436CU
MBRL040	MBRS130LT3G	MBRS360T3G	MC1436D
MBRM110ET1G	MBRS130T3G	MBRS410ET3G	MC1436G
MBRM110ET3G	MBRS140T3	MBRS410LT3	MC1436P1

Multisim 14.0 Power Pro Components

MC1436U	MC1537L	MC1747CD	MC3303L
MC1437L	MC1539G	MC1747CG	MC3303P
MC1437P	MC1556G	MC1747CL	MC33071ADG
MC1439G	MC1556U	MC1747CP2	MC33071ADR2G
MC1439P1	MC1558FK	MC1747G	MC33071AP
MC1456CG	MC1558G	MC1747L	MC33071APG
MC1456CP1	MC1558JG	MC1748CG	MC33071D
MC1456G	MC1558SG	MC1748CP1	MC33071DG
MC1456P1	MC1558SU	MC1748CU	MC33071DR2G
MC1458CD	MC1558U	MC1748G	MC33071P
MC1458CG	MC1709AG	MC1748U	MC33071PG
MC1458CP1	MC1709AU	MC1776CD	MC33071U
MC1458CU	MC1709CG	MC1776CG	MC33072ADG
MC1458D	MC1709CP1	MC1776CP1	MC33072ADR2G
MC1458G	MC1709CU	MC1776CU	MC33072AP
MC1458P	MC1709G	MC1776G	MC33072APG
MC1458P1	MC1741CD	MC1776U	MC33072D
MC1458SD	MC1741CG	MC3301P	MC33072DG
MC1458SG	MC1741CP1	MC3302D	MC33072DR2G
MC1458SP1	MC1741CU	MC3302DG	MC33072P
MC1458SU	MC1741G	MC3302DR2G	MC33072PG
MC1458U	MC1741SCD	MC3302DTBR2G	MC33072U
MC1503U	MC1741SCG	MC3302P	MC33074ADG
MC1536G	MC1741SCP1	MC3302PG	MC33074ADR2G
MC1536U	MC1741U	MC3303D	MC33074ADTBG

Multisim 14.0 Power Pro Components

MC33074ADTBR2G	MC33079DR2G	MC33179DTBR2G	MC33364D2R2G
MC33074APG	MC33079P	MC33179P	MC3358P1
MC33074D	MC33079PG	MC33179PG	MC34001D
MC33074DG	MC33161DG	MC33181D	MC34001G
MC33074DR2G	MC33161DMR2G	MC33181P	MC34001P
MC33074DTBG	MC33161DR2G	MC33182D	MC34001U
MC33074DTBR2G	MC33161PG	MC33182P	MC3401D
MC33074L	MC33171D	MC33184D	MC3401P
MC33074P	MC33171DG	MC33184P	MC3403D
MC33074PG	MC33171DR2G	MC33272ADG	MC3403DG
MC33076D	MC33171P	MC33272APG	MC3403DR2G
MC33076P1	MC33171PG	MC33272D	MC3403L
MC33076P2	MC33172D	MC33272P	MC3403N
MC33077D	MC33172P	MC33274ADG	MC3403P
MC33077DG	MC33174D	MC33274ADTBR2G	MC3403PG
MC33077DR2G	MC33174P	MC33274APG	MC3405L
MC33077P	MC33178D	MC33274D	MC3405P
MC33077PG	MC33178DG	MC33274P	MC34063ADG
MC33078D	MC33178DMR2G	MC33282D	MC34063ADR2G
MC33078DG	MC33178DR2G	MC33282P	MC34063AP1G
MC33078DR2G	MC33178P	MC33284D	MC34071D
MC33078P	MC33178PG	MC33284P	MC34071P
MC33078PG	MC33179D	MC33364D1G	MC34071U
MC33079D	MC33179DG	MC33364D1R2G	MC34080D
MC33079DG	MC33179DR2G	MC33364D2G	MC34080P

Multisim 14.0 Power Pro Components

MC34084DW	MC35080AU	MC74AC245N	MC7815CT
MC34084P	MC35080U	MC74AC620DW	MC7818ACT
MC34161DG	MC35171U	MC74AC620N	MC7818BT
MC34161DMR2G	MC35181U	MC74AC623DW	MC7818CT
MC34161DR2G	MC3558G	MC74AC623N	MC7824ACT
MC34161PG	MC3558U	MC74ACT245DW	MC7824BT
MC34181D	MC4558ACP1	MC74ACT245N	MC7824CT
MC34181P	MC4558CD	MC74ACT623DW	MC78L05ACD
MC3458D	MC4558CG	MC74ACT623N	MC78L05ACP
MC3458G	MC4558CP1	MC74HC4066D	MC78L05CP
MC3458P1	MC4558CU	MC74HC4066D	MC78L08CP
MC3458U	MC4558G	MC74HC4066J	MC78L09ACD
MC3476G	MC4558U	MC74HC4066N	MC78L09ACP
MC3476P1	MC4741CD	MC7805BT	MC78L09CP
MC3476U	MC4741CL	MC7805CT	MC78L12ACD
MC3486D	MC4741CP	MC7806BT	MC78L12ACP
MC3486L	MC4741L	MC7806CT	MC78L15ACD
MC3486P	MC68HC11D3CFBL	MC7808ACT	MC78L15ACP
MC3487D	MC68HC11D3CFN1	MC7808BT	MC78L18ACP
MC35001G	MC68HC11D3CP1	MC7808CT	MC78L18CP
MC35001U	MC68HC11E0CFN2	MC7809CT	MC78L24ACP
MC3503L	MC68HC11E1CFN2	MC7812ACT	MC78L24CP
MC3505L	MC74AC240DW	MC7812BT	MCH3209-TL-E
MC35071AU	MC74AC240N	MC7812CT	MCH3377-TL-E
MC35071U	MC74AC245DW	MC7815BT	MCH3377-TL-H

Multisim 14.0 Power Pro Components

MCH3383-TL-H	MCP6002-I/MS	MCP6023-I/ST	MCP6042-I/P
MCH3474-TL-E	MCP6002-I/P	MCP6024-I/P	MCP6042-I/SN
MCH3474-TL-H	MCP6002-I/SN	MCP6024-I/SL	MCP6043-I/MS
MCH3484-TL-H	MCP6002T-E/MS	MCP6024-I/ST	MCP6043-I/P
MCH6203-TL-E	MCP6002T-E/SN	MCP602T-I/P	MCP6043-I/SN
MCH6320-TL-E	MCP6004-E/P	MCP602T-I/SN	MCP6043T-I/CH
MCH6321-TL-E	MCP6004-I/P	MCP602T-I/ST	MCP6044-I/P
MCH6336-TL-E	MCP6004-I/SL	MCP6031-E/MS	MCP6044-I/SL
MCH6336-TL-H	MCP6004-I/ST	MCP6031-E/SN	MCP6044-I/ST
MCH6337-TL-E	MCP6004T-E/SL	MCP6031T-E/OT	MCP604T-I/P
MCH6337-TL-H	MCP6004T-E/ST	MCP6032-E/MS	MCP604T-I/SL
MCH6421-TL-E	MCP601-I/P	MCP6032-E/SN	MCP604T-I/ST
MCH6436-TL-E	MCP601-I/SN	MCP6033-E/MS	MCP6051T-E/MNY
MCH6534-TL-E	MCP601-I/ST	MCP6033-E/SN	MCP6051T-E/OT
MCH6604-TL-E	MCP601T-I/OT	MCP6034-E/SL	MCP6051T-E/SN
MCP6001RT-E/OT	MCP6021-E/MS	MCP6034-E/ST	MCP6052T-E/MNY
MCP6001RT-I/OT	MCP6021-I/P	MCP603T-I/CH	MCP6052T-E/SN
MCP6001T-E/LT	MCP6021-I/SN	MCP603T-I/P	MCP6054T-E/SL
MCP6001T-E/OT	MCP6021-I/ST	MCP603T-I/SN	MCP6054T-E/ST
MCP6001T-I/LT	MCP6021T-E/OT	MCP603T-I/ST	MCP6061T-E/MNY
MCP6001T-I/OT	MCP6022-I/P	MCP6041-I/MS	MCP6061T-E/OT
MCP6001UT-E/OT	MCP6022-I/SN	MCP6041-I/P	MCP6061T-E/SN
MCP6001UT-I/OT	MCP6022-I/ST	MCP6041-I/SN	MCP6062T-E/MNY
MCP6002-E/MC	MCP6023-I/P	MCP6041T-I/OT	MCP6062T-E/SN
MCP6002-E/P	MCP6023-I/SN	MCP6042-I/MS	MCP6064T-E/SL

Multisim 14.0 Power Pro Components

MCP6064T-E/ST	MCP6142-I/MS	MCP622T-E/MF	MCP6241UT-E/OT
MCP606-I/P	MCP6142-I/P	MCP622T-E/SN	MCP6242-E/MS
MCP606-I/SN	MCP6142-I/SN	MCP6231-E/MC	MCP6242-E/P
MCP606-I/ST	MCP6143-I/MS	MCP6231-E/MS	MCP6242-E/SN
MCP606T-I/OT	MCP6143-I/P	MCP6231-E/P	MCP6244-E/P
MCP6071T-E/MNY	MCP6143-I/SN	MCP6231-E/SN	MCP6244-E/SL
MCP6071T-E/OT	MCP6143T-E/CH	MCP6231RT-E/OT	MCP6244-E/ST
MCP6071T-E/SN	MCP6144-I/P	MCP6231T-E/OT	MCP624T-E/SL
MCP6072T-E/MNY	MCP6144-I/SL	MCP6231UT-E/LT	MCP624T-E/ST
MCP6072T-E/SN	MCP6144-I/ST	MCP6231UT-E/OT	MCP625T-E/MF
MCP6074T-E/SL	MCP616-I/MS	MCP6232-E/MS	MCP625T-E/UN
MCP6074T-E/ST	MCP616-I/P	MCP6232-E/P	MCP6271-E/MS
MCP607-I/P	MCP616-I/SN	MCP6232-E/SN	MCP6271-E/P
MCP607-I/SN	MCP617-I/MS	MCP6232T-E/MNY	MCP6271-E/SN
MCP607-I/ST	MCP617-I/P	MCP6234-E/P	MCP6271RT-E/OT
MCP608-I/P	MCP617-I/SN	MCP6234-E/SL	MCP6271T-E/OT
MCP608-I/SN	MCP618-I/MS	MCP6234-E/ST	MCP6272-E/MS
MCP608-I/ST	MCP618-I/P	MCP623T-E/CHY	MCP6272-E/P
MCP609-I/P	MCP618-I/SN	MCP6241-E/MC	MCP6272-E/SN
MCP609-I/SL	MCP619-I/P	MCP6241-E/MS	MCP6273-E/MS
MCP609-I/ST	MCP619-I/SL	MCP6241-E/P	MCP6273-E/P
MCP6141-I/MS	MCP619-I/ST	MCP6241-E/SN	MCP6273-E/SN
MCP6141-I/P	MCP621ST-E/OT	MCP6241RT-E/OT	MCP6273T-E/CH
MCP6141-I/SN	MCP621T-E/MNY	MCP6241T-E/OT	MCP6273T-E/SN
MCP6141T-E/OT	MCP621T-E/SN	MCP6241UT-E/LT	MCP6274-E/P

Multisim 14.0 Power Pro Components

MCP6274-E/SL	MCP6291-E/P	MCP635T-E/MF	MCP6471T-E/LTY
MCP6274-E/ST	MCP6291-E/SN	MCP635T-E/UN	MCP6471T-E/OT
MCP6275-E/MS	MCP6291RT-E/OT	MCP6401RT-E/OT	MCP6472-E/MS
MCP6275-E/P	MCP6291T-E/OT	MCP6401T-E/LT	MCP6472-E/SN
MCP6275-E/SN	MCP6292-E/MS	MCP6401T-E/OT	MCP6472T-E/MNY
MCP6281-E/MS	MCP6292-E/P	MCP6401T-H/OT	MCP6472T-E/MS
MCP6281-E/P	MCP6292-E/SN	MCP6401UT-E/OT	MCP6472T-E/SN
MCP6281-E/SN	MCP6293-E/MS	MCP6402T-E/MNY	MCP6474-E/SL
MCP6281RT-E/OT	MCP6293-E/P	MCP6402T-E/SN	MCP6474-E/ST
MCP6281T-E/OT	MCP6293-E/SN	MCP6402T-H/SN	MCP6474T-E/SL
MCP6282-E/MS	MCP6293T-E/CH	MCP6404T-E/SL	MCP6474T-E/ST
MCP6282-E/P	MCP6294-E/P	MCP6404T-E/ST	MCP6481T-E/LTY
MCP6282-E/SN	MCP6294-E/SL	MCP6404T-H/SL	MCP6481T-E/OT
MCP6283-E/MS	MCP6294-E/ST	MCP6406T-H/OT	MCP6482-E/MS
MCP6283-E/P	MCP6295-E/MS	MCP6407T-H/SN	MCP6482-E/SN
MCP6283-E/SN	MCP6295-E/P	MCP6409T-H/SL	MCP6482T-E/MNY
MCP6283T-E/CH	MCP6295-E/SN	MCP6421T-E/LTY	MCP6482T-E/MS
MCP6284-E/P	MCP629T-E/ML	MCP6421T-E/OT	MCP6482T-E/SN
MCP6284-E/SL	MCP631T-E/MNY	MCP6441T-E/LT	MCP6484-E/SL
MCP6284-E/ST	MCP631T-E/OT	MCP6441T-E/OT	MCP6484-E/ST
MCP6285-E/MS	MCP631T-E/SN	MCP6442T-E/MNY	MCP6484T-E/SL
MCP6285-E/P	MCP632T-E/MF	MCP6442T-E/MS	MCP6484T-E/ST
MCP6285-E/SN	MCP632T-E/SN	MCP6442T-E/SN	MCP6491T-E/LTY
MCP6286T-E/OT	MCP633T-E/CHY	MCP6444T-E/SL	MCP6491T-E/OT
MCP6291-E/MS	MCP633T-E/SN	MCP6444T-E/ST	MCP6492-E/MS

Multisim 14.0 Power Pro Components

MCP6492-E/SN	MCP6541UT-I/LT	MCP6546T-E/MS	MCP6549-E/P
MCP6492T-E/MNY	MCP6542-E/P	MCP6546T-E/OT	MCP6549-I/P
MCP6492T-E/MS	MCP6542-I/MS	MCP6546T-E/SN	MCP6549-I/SL
MCP6492T-E/SN	MCP6542-I/P	MCP6546T-I/LT	MCP6549-I/ST
MCP6494-E/SL	MCP6542-I/SN	MCP6546T-I/MS	MCP6549T-E/SL
MCP6494-E/ST	MCP6542T-E/MS	MCP6546T-I/OT	MCP6549T-E/ST
MCP6494T-E/SL	MCP6542T-E/SN	MCP6546T-I/SN	MCP6549T-I/SL
MCP6494T-E/ST	MCP6543-E/P	MCP6546UT-E/OT	MCP6549T-I/ST
MCP651ST-E/OT	MCP6543-I/P	MCP6546UT-I/LT	MCP654T-E/SL
MCP651T-E/MNY	MCP6543-I/SN	MCP6547-E/P	MCP654T-E/ST
MCP651T-E/SN	MCP6543T-E/MS	MCP6547-I/MS	MCP655T-E/MF
MCP652T-E/MF	MCP6543T-E/SN	MCP6547-I/P	MCP655T-E/UN
MCP652T-E/SN	MCP6543T-I/MS	MCP6547-I/SN	MCP6561RT-E/OT
MCP653T-E/CHY	MCP6544-E/P	MCP6547T-E/MS	MCP6561T-E/LT
MCP6541-E/P	MCP6544T-E/SL	MCP6547T-E/SN	MCP6561T-E/OT
MCP6541-I/MS	MCP6544T-E/ST	MCP6547T-I/MS	MCP6561UT-E/OT
MCP6541-I/P	MCP6544T-I/P	MCP6547T-I/SN	MCP6562T-E/MS
MCP6541-I/SN	MCP6544T-I/SL	MCP6548-E/P	MCP6562T-E/SN
MCP6541RT-E/OT	MCP6544T-I/ST	MCP6548-I/MS	MCP6564T-E/SL
MCP6541T-E/MS	MCP6546-E/P	MCP6548-I/P	MCP6564T-E/ST
MCP6541T-E/OT	MCP6546-I/MS	MCP6548-I/SN	MCP6566RT-E/OT
MCP6541T-E/SN	MCP6546-I/P	MCP6548T-E/MS	MCP6566T-E/LT
MCP6541T-I/LT	MCP6546-I/SN	MCP6548T-E/SN	MCP6566T-E/OT
MCP6541T-I/OT	MCP6546RT-E/OT	MCP6548T-I/MS	MCP6566UT-E/OT
MCP6541UT-E/OT	MCP6546RT-I/OT	MCP6548T-I/SN	MCP6567T-E/MS

Multisim 14.0 Power Pro Components

MCP6567T-E/SN	MCP669T-E/ML	MCP6H84T-E/SL	MCP6L71T-E/MS
MCP6569T-E/SL	MCP6H01T-E/MNY	MCP6H84T-E/ST	MCP6L71T-E/OT
MCP6569T-E/ST	MCP6H01T-E/SN	MCP6H91T-E/MNY	MCP6L71T-E/SN
MCP659T-E/ML	MCP6H02T-E/MNY	MCP6H91T-E/SN	MCP6L72T-E/MS
MCP65R41T- 1202E/CHY	MCP6H02T-E/SN	MCP6H92T-E/MNY	MCP6L72T-E/SN
	MCP6H04T-E/SL	MCP6H92T-E/SN	MCP6L74T-E/SL
MCP65R41T- 2402E/CHY	MCP6H04T-E/ST	MCP6H94T-E/SL	MCP6L74T-E/ST
	MCP6H71-E/SN	MCP6H94T-E/ST	MCP6L91RT-E/OT
MCP65R46T- 1202E/CHY	MCP6H71T-E/MNY	MCP6L01RT-E/OT	MCP6L91T-E/MS
	MCP6H71T-E/SN	MCP6L01T-E/LT	MCP6L91T-E/OT
MCP65R46T- 2402E/CHY	MCP6H72-E/SN	MCP6L01T-E/OT	MCP6L91T-E/SN
	MCP6H72T-E/MNY	MCP6L01UT-E/OT	MCP6L92T-E/MS
MCP660T-E/ML	MCP6H72T-E/SN	MCP6L02T-E/MS	MCP6L92T-E/SN
MCP660T-E/SL	MCP6H74-E/SL	MCP6L02T-E/SN	MCP6L94T-E/SL
MCP660T-E/ST	MCP6H74-E/ST	MCP6L04T-E/SL	MCP6L94T-E/ST
MCP661T-E/OT	MCP6H74T-E/SL	MCP6L04T-E/ST	MCP6N11-001E/SN
MCP661T-E/SN	MCP6H74T-E/ST	MCP6L1RT-E/OT	MCP6N11T- 001E/MNY
MCP662T-E/MF	MCP6H81-E/SN	MCP6L1T-E/MS	MCP6V01T-E/MNY
MCP662T-E/MS	MCP6H81T-E/MNY	MCP6L1T-E/OT	
MCP662T-E/SN	MCP6H81T-E/SN	MCP6L1T-E/SN	MCP6V01T-E/SN
MCP663T-E/CHY	MCP6H82-E/SN	MCP6L2T-E/MS	MCP6V02-E/MD
MCP663T-E/SN	MCP6H82T-E/MNY	MCP6L2T-E/SN	MCP6V02-E/SN
MCP664T-E/SL	MCP6H82T-E/SN	MCP6L4T-E/SL	MCP6V03-E/MNY
MCP664T-E/ST	MCP6H84-E/SL	MCP6L4T-E/ST	MCP6V03-E/SN
MCP665T-E/MF	MCP6H84-E/ST	MCP6L71RT-E/OT	MCP6V06-E/SN
MCP665T-E/UN			

Multisim 14.0 Power Pro Components

MCP6V06T-E/MNY	MCR1906_3	MCR265_10	MCR3935_3
MCP6V07-E/MD	MCR1906_4	MCR265_2	MCR3935_4
MCP6V07-E/SN	MCR1906_6	MCR265_3	MCR3935_5
MCP6V08-E/SN	MCR1906_8	MCR265_4	MCR3935_6
MCP6V08T-E/MNY	MCR218_10FP	MCR265_6	MCR3935_7
MCP6V11T-E/OT	MCR218_2FP	MCR265_8	MCR3935_8
MCP6V11UT-E/LT	MCR218_4FP	MCR3818_10	MCR3935_9
MCP6V11UT-E/OT	MCR218_6FP	MCR3818_2	MCR703AT4G
MCP6V26T-E/MNY	MCR218_8FP	MCR3818_3	MCR706AT4G
MCP6V26T-E/MS	MCR22_2	MCR3818_4	MCR716T4G
MCP6V26T-E/SN	MCR22_3	MCR3818_6	MCR8SNG
MCP6V27T-E/MD	MCR22_4	MCR3818_8	MCT2
MCP6V27T-E/MS	MCR22_6	MCR3835_1	MCT2E
MCP6V27T-E/SN	MCR22_8	MCR3835_10	MCT6
MCP6V28T-E/MNY	MCR220_5	MCR3835_2	MDA2500
MCP6V28T-E/MS	MCR220_7	MCR3835_3	MDA2501
MCP6V28T-E/SN	MCR220_9	MCR3835_4	MDA2502
MCP6V31T-E/OT	MCR221_5	MCR3835_5	MDA2504
MCP6V31UT-E/LT	MCR221_7	MCR3835_6	MDA2506
MCP6V31UT-E/OT	MCR221_9	MCR3835_7	MDA3500
MCR08BT1G	MCR225_10FP	MCR3835_8	MDA3501
MCR08MT1G	MCR225_2FP	MCR3835_9	MDA3502
MCR100-3G	MCR225_4FP	MCR3935_1	MDA3504
MCR100-3RLG	MCR225_6FP	MCR3935_10	MDA3506
MCR1906_2	MCR225_8FP	MCR3935_2	MDA3508

Multisim 14.0 Power Pro Components

MDA3510	MDA990-3	MJ11015G	MJ15016G
MDA3550	MDA990-4	MJ11016G	MJ15022
MDA3551	MDA990-5	MJ11017	MJ15022G
MDA920A1	MDA990-6	MJ11021	MJ15023
MDA920A2	MGP11N60ED	MJ11028G	MJ15023G
MDA920A3	MGSF1N02LT1G	MJ11032	MJ15024
MDA920A4	MGSF1N03LT1G	MJ11032G	MJ15024G
MDA920A5	MGSF1P02LT1	MJ11033	MJ15025
MDA920A6	MGSF2N02ELT1G	MJ11033G	MJ15025G
MDA920A7	MGSF3441VT1	MJ112	MJ16010
MDA920A8	MGW21N60ED	MJ112-1	MJ16012
MDA920A9	MHD20N06C	MJ112T4	MJ16110
MDA970A1	MHD20N06G	MJ122	MJ21193
MDA970A2	MHD20N06P	MJ122-1	MJ21193G
MDA970A3	MICRO_4BIT_ALU	MJ122T4	MJ21194
MDA970A5	MINI-DIN3	MJ13333	MJ21194G
MDA970A6	MINI-DIN3S	MJ14002G	MJ21195G
MDA980-1	MINI-DIN4	MJ15001	MJ21196G
MDA980-2	MINI-DIN4S	MJ15001G	MJ2955G
MDA980-3	MINI-DIN5	MJ15002	MJ4502
MDA980-4	MINI-DIN5S	MJ15003G	MJ4502G
MDA980-5	MINI-DIN6	MJ15004G	MJ802
MDA980-6	MINI-DIN6S	MJ15015	MJ802G
MDA990-1	MIPS-EJTAG-HDR	MJ15015G	MJB41CG
MDA990-2	MJ11012G	MJ15016	MJB41CT4G

Multisim 14.0 Power Pro Components

MJB42CT4G	MJD148T4	MJD2955T4G	MJD32T4G
MJB44H11G	MJD148T4G	MJD3055	MJD340G
MJB44H11T4	MJD200	MJD3055-1	MJD340RLG
MJB44H11T4G	MJD200G	MJD3055G	MJD340T4G
MJB45H11G	MJD200RLG	MJD3055T4G	MJD350G
MJB45H11T4	MJD200T4G	MJD3055TR	MJD350T4G
MJB45H11T4G	MJD210	MJD31	MJD41CRLG
MJD112	MJD210-1	MJD31-1	MJD41CT4G
MJD112-1G	MJD210G	MJD31C	MJD42C1G
MJD112G	MJD210RLG	MJD31C-1	MJD42CG
MJD112RLG	MJD210T4	MJD31C1G	MJD42CRLG
MJD112T4G	MJD210T4G	MJD31CG	MJD42CT4G
MJD117	MJD243	MJD31CRLG	MJD44E3T4G
MJD117-1	MJD243-1	MJD31CT4G	MJD44H11
MJD117-1G	MJD243G	MJD31CTR	MJD44H11-1
MJD117G	MJD243T4	MJD31T4G	MJD44H11-1G
MJD117RLG	MJD243T4G	MJD31TR	MJD44H11G
MJD117T4	MJD253-1G	MJD32	MJD44H11RLG
MJD117T4G	MJD253T4	MJD32-1	MJD44H11T4G
MJD122G	MJD253T4G	MJD32CG	MJD44H11T5G
MJD122T4G	MJD2955	MJD32CRLG	MJD44H11TR
MJD127	MJD2955-1	MJD32CT4	MJD45H11
MJD127G	MJD2955-1G	MJD32CT4G	MJD45H11-1
MJD127T4	MJD2955G	MJD32RLG	MJD45H11-1G
MJD127T4G	MJD2955T4	MJD32T4.CMP	MJD45H11G

Multisim 14.0 Power Pro Components

MJD45H11RLG	MJE15029	MJE180G	MJE344
MJD45H11T4	MJE15029G	MJE181	MJE3440
MJD45H11T4G	MJE15030	MJE181G	MJE344G
MJD47	MJE15030G	MJE182	MJE350
MJD47-1	MJE15031	MJE18204	MJE350G
MJD47G	MJE15031G	MJE182G	MJE371G
MJD47T4G	MJE15032	MJE200	MJE4343
MJD47TR	MJE15032G	MJE200G	MJE4343G
MJD50	MJE15033	MJE210	MJE4353
MJD50-1	MJE15033G	MJE210G	MJE4353G
MJD50G	MJE15034G	MJE243	MJE5730
MJD50T4G	MJE15035G	MJE243G	MJE5730G
MJD50TR	MJE16002	MJE253	MJE5731
MJD5731T4G	MJE16004	MJE253G	MJE5731AG
MJD6039T4G	MJE170G	MJE270G	MJE5731G
MJE13003	MJE171	MJE271G	MJE5742G
MJE13003G	MJE171G	MJE2955T	MJE5850G
MJE13005	MJE172	MJE2955TG	MJE5851G
MJE13005G	MJE172G	MJE3055T	MJE5852G
MJE13007	MJE18002G	MJE3055TG	MJE700G
MJE13007G	MJE18004	MJE340	MJE702G
MJE13009G	MJE18004G	MJE340G	MJE703G
MJE1320	MJE18006	MJE341	MJE800G
MJE15028	MJE18006G	MJE3439	MJE802G
MJE15028G	MJE18008G	MJE3439G	MJE803G

Multisim 14.0 Power Pro Components

MJF122G	MJL21194G	MM3Z2V7T1G	MM5Z2V7T1G
MJF127G	MJL21195G	MM3Z30VT1G	MM5Z33VT1G
MJF15030G	MJL21196G	MM3Z36VT1G	MM5Z36VT1G
MJF15031G	MJL3281A	MM3Z39VT1G	MM5Z3V0T1G
MJF18004G	MJL3281AG	MM3Z3V0T1G	MM5Z3V3T1G
MJF18008G	MJL4281AG	MM3Z3V3ST1G	MM5Z3V6T1G
MJF2955	MJL4302AG	MM3Z3V6T1G	MM5Z47VT1G
MJF2955G	MJW16010	MM3Z3V9T1G	MM5Z4V3T1G
MJF3055G	MJW16012	MM3Z43VT1G	MM5Z4V7ST1G
MJF31CG	MJW16018	MM3Z4V3ST1G	MM5Z4V7ST5G
MJF32CG	MJW18020G	MM3Z4V7T1G	MM5Z4V7T1G
MJF44H11G	MJW21196G	MM3Z5V1T1G	MM5Z5V1ST1G
MJF45H11G	MJW3281AG	MM3Z5V6ST1G	MM5Z5V1T1G
MJF6107	MKP3V120G	MM3Z6V8ST1G	MM5Z5V6ST1G
MJH11021G	MKP3V120RLG	MM3Z8V2ST1G	MM5Z5V6T1G
MJH11022G	MKP3V240G	MM5Z10VT1G	MM5Z6V2ST1G
MJH6284	MKP3V240RLG	MM5Z12VT1G	MM5Z6V2T1G
MJH6284G	MM3Z10VT1G	MM5Z15VT1G	MM5Z6V8ST1G
MJH6287	MM3Z12VST1G	MM5Z16VT1G	MM5Z6V8T1G
MJH6287G	MM3Z12VT1G	MM5Z18VT1G	MM5Z7V5T1G
MJL1302A	MM3Z15VST1G	MM5Z20VT1G	MM5Z8V2ST1G
MJL1302AG	MM3Z15VT1G	MM5Z24VT1G	MM5Z8V2T1G
MJL21193	MM3Z18VT1G	MM5Z27VT1G	MM5Z9V1ST1G
MJL21193G	MM3Z20VT1G	MM5Z2V4ST1G	MM5Z9V1T1G
MJL21194	MM3Z2V4T1G	MM5Z2V4T1G	MMBD101LT1G

Multisim 14.0 Power Pro Components

MMBD1201	MMBF0201NLT1G	MMBR951LT1	MMBT4403LT1G
MMBD1202	MMBF170LT1G	MMBT2222A	MMBT4403LT3G
MMBD1203	MMBF4393LT1G	MMBT2222ALT1	MMBT4403M3T5G
MMBD1204	MMBF4393LT3G	MMBT2222ALT1G	MMBT489LT1G
MMBD1205	MMBF5460LT1	MMBT2222ALT3G	MMBT5401LT1
MMBD2835LT1G	MMBFJ175LT1G	MMBT2369ALT1G	MMBT5401LT1G
MMBD2836LT1G	MMBFJ177LT1G	MMBT2484LT1G	MMBT5401LT3G
MMBD2837LT1G	MMBFJ309LT1G	MMBT2484LT3G	MMBT5551LT1
MMBD2838LT1G	MMBFJ310LT1	MMBT2907ALT1	MMBT5551LT1G
MMBD301LT1	MMBFU310LT1	MMBT2907ALT1G	MMBT5551LT3G
MMBD301LT1G	MMBR5031LT1	MMBT2907ALT3G	MMBT5551M3T5G
MMBD301LT3G	MMBR521LT1	MMBT2907AM3T5G	MMBT589LT1
MMBD301M3T5G	MMBR571L	MMBT3904	MMBT589LT1G
MMBD352LT1G	MMBR571LT1	MMBT3904LT1	MMBT6427LT1
MMBD353LT1G	MMBR901_B	MMBT3904LT1G	MMBT6428LT1G
MMBD4148	MMBR901L	MMBT3904LT3G	MMBT6429LT1G
MMBD7000LT1	MMBR901LT1	MMBT3904TT1G	MMBT6517LT1
MMBD7000LT1G	MMBR911LT1	MMBT3906	MMBT6517LT1G
MMBD7000LT3G	MMBR920LT1	MMBT3906TT1G	MMBT6517LT3G
MMBD717LT1G	MMBR931L	MMBT4401LT1	MMBT6520LT1
MMBD914	MMBR931LT1	MMBT4401LT1G	MMBT6520LT1G
MMBD914LT1	MMBR941	MMBT4401LT3G	MMBTA06LT1
MMBD914LT1G	MMBR941LT1	MMBT4401M3T5G	MMBTA06LT1G
MMBD914LT3G	MMBR951AL	MMBT4403LT1	MMBTA06LT3G
MMBF0201NLT1	MMBR951L		MMBTA06WT1G

Multisim 14.0 Power Pro Components

MMBTA13L	MMBZ10VAL	MMBZ5231BLT3G	MMJT350T1G
MMBTA13LT1	MMBZ12VAL	MMBZ5232BLT1G	MMJT9410
MMBTA14LT1G	MMBZ12VDL	MMBZ5240BLT1G	MMQA15VT1G
MMBTA42	MMBZ15VAL	MMBZ5242BLT1G	MMQA20VT1G
MMBTA42LT1	MMBZ15VALT1	MMBZ5242BLT3G	MMQA20VT3G
MMBTA42LT1G	MMBZ15VALT1G	MMBZ5248BLT1G	MMQA5V6T1G
MMBTA42LT3G	MMBZ15VDL	MMBZ5248BLT3G	MMQA5V6T3G
MMBTA56LT1	MMBZ15VDLT1G	MMBZ5254BLT1G	MMQA6V2T1G
MMBTA56LT1G	MMBZ15VDLT3G	MMBZ5256BLT1G	MMSD301T1
MMBTA56LT3G	MMBZ18VAL	MMBZ5270BLT1G	MMSD301T1G
MMBTA63LT1G	MMBZ18VCL	MMBZ5V6AL	MMSD4148T1
MMBTA92	MMBZ20VAL	MMBZ5V6ALT1G	MMSD4148T1G
MMBTA92LT1G	MMBZ20VALT1G	MMBZ5V6ALT3G	MMSD4148T3G
MMBTA92LT3G	MMBZ20VCL	MMBZ6V2AL	MMSF3P02HD
MMBTH10-4LT1G	MMBZ27VAL	MMBZ6V8AL	MMSZ10T1G
MMBTH10LT1G	MMBZ27VALT1G	MMBZ9V1AL	MMSZ12T1G
MMBTH10LT3G	MMBZ27VALT3G	MMDF3N04HD	MMSZ2V7T1G
MMBV105GLT1	MMBZ27VCL	MMDF6N03HD	MMSZ2V7T3G
MMBV105GLT1G	MMBZ27VCLT1G	MMDL770T1G	MMSZ3V3T1G
MMBV109LT1	MMBZ33VAL	MMDL914T1	MMSZ4678T1G
MMBV3102LT1	MMBZ33VALT1G	MMDL914T1G	MMSZ4679T1G
MMBV3401LT1G	MMBZ33VCL	MMDL914T3G	MMSZ4681T1G
MMBV3401LT3	MMBZ5221BLT1G	MMFT5P03HD	MMSZ4683T1G
MMBV3401LT3G	MMBZ5222BLT1G	MMFT960T1G	MMSZ4688T1G
MMBV609LT1	MMBZ5231BLT1G	MMG05N60D	MMSZ4689T1G

Multisim 14.0 Power Pro Components

MMSZ4689T3G	MMSZ5242BT3G	MMUN2112LT1G	MOC1006
MMSZ4690T1G	MMSZ5243BT1G	MMUN2113LT1G	MOC205
MMSZ4690T3G	MMSZ5245BT1G	MMUN2113LT3G	MOC206
MMSZ4691T1G	MMSZ5246BT1G	MMUN2114LT1G	MOC207
MMSZ4692T1G	MMSZ5254BT1G	MMUN2114LT3G	MOC211
MMSZ4696T1G	MMSZ5258BT1G	MMUN2115LT1G	MOC212
MMSZ4699T1G	MMSZ5258BT3G	MMUN2116LT1G	MOC213
MMSZ4705T1G	MMSZ5259BT1G	MMUN2130LT1G	MOC215
MMSZ4706T1G	MMSZ5260BT1G	MMUN2131LT1G	MOC216
MMSZ4707T1G	MMSZ5262BT1G	MMUN2132LT1G	MOC217
MMSZ4715T1G	MMSZ5263BT1G	MMUN2134LT1G	MOC223
MMSZ5221BT1G	MMT05B230T3G	MMUN2211LT1G	MOC8100
MMSZ5222BT1G	MMT05B260T3G	MMUN2211LT3G	MOC8101
MMSZ5225BT1G	MMT05B310T3G	MMUN2212LT1G	MOC8101_BASSO
MMSZ5226BT1G	MMT05B350T3G	MMUN2213LT1G	MOC8102
MMSZ5228BT1G	MMT08B064T3G	MMUN2214LT1G	MOC8103
MMSZ5231BT1G	MMT08B260T3G	MMUN2215LT1G	MOC8104
MMSZ5231BT3G	MMT08B310T3G	MMUN2216LT1G	MOC8111
MMSZ5234BT1G	MMT08B350T3G	MMUN2231LT1G	MOC8112
MMSZ5235BT1G	MMT10B230T3G	MMUN2232LT1G	MOC8113
MMSZ5235BT3G	MMT10B260T3G	MMUN2233LT1G	MOCD213
MMSZ5236BT1G	MMT10B310T3G	MMUN2234LT1G	MONOSTABLE_VIRTUAL
MMSZ5239BT1G	MMT10B350T3G	MMUN2238LT1G	MOS_N
MMSZ5240BT1G	MMUN2111LT1G	MMVL3401T1G	MOS_N_4T
MMSZ5242BT1G	MMUN2111LT3G	MOC1005	

Multisim 14.0 Power Pro Components

MOS_N_4T_DEP	MPC507AP	MPS3703	MPS6566
MOS_N_DEP	MPC507AU	MPS3704	MPS6571
MOS_P	MPC508AP	MPS3707	MPS6601
MOS_P_4T	MPC508AU	MPS3711	MPS6651
MOS_P_4T_DEP	MPC509AP	MPS3826	MPS8098
MOS_P_DEP	MPC509AU	MPS3827	MPS8099
MOSFET_DIODE_TH ERMAL	MPC-BDM-HDR	MPS3904	MPS8598
	MPF910	MPS5172	MPS8599
MOTOR_1A	MPF960	MPS5179	MPSA05
MOTOR_1C	MPS2222	MPS6512	MPSA06
MOTOR_2A	MPS2907	MPS6513	MPSA06G
MOTOR_2C	MPS2907AG	MPS6514	MPSA06RL1G
MOTOR_3A	MPS2907ARLG	MPS6515	MPSA06RLG
MOTOR_3C	MPS2907ARLRAG	MPS6516	MPSA06RLRAG
MOTOR_4A	MPS2924	MPS6517	MPSA06RLRMG
MOTOR_4C	MPS2925	MPS6518	MPSA06RLRPG
MOTOR_RATED	MPS2926	MPS6520	MPSA10
MOTOR_VIRTUAL	MPS3392	MPS6521	MPSA13
MPC100AP	MPS3393	MPS6522	MPSA14
MPC100AU	MPS3395	MPS6523	MPSA18
MPC102AP	MPS3638A	MPS6531	MPSA20
MPC102AU	MPS3640	MPS6533	MPSA42
MPC104AP	MPS3644	MPS6534	MPSA42G
MPC506AP	MPS3646	MPS6562	MPSA43
MPC506AU	MPS3702	MPS6565	MPSA43G

Multisim 14.0 Power Pro Components

MPSA44	MPSW51ARLRPG	MR2500	MR510
MPSA55	MPSW51G	MR2501	MR750
MPSA56	MPSW55	MR2502	MR751
MPSA56G	MPSW56	MR2504	MR752
MPSA56RLRAG	MPSW92	MR2506	MR754
MPSA56RLRMG	MPZ2012S101A	MR2508	MR756
MPSA56RLRPG	MPZ2012S221A	MR2510	MR810
MPSA56ZL1G	MPZ2012S300A	MR327	MR811
MPSA70	MPZ2012S331A	MR328	MR812
MPSA92	MPZ3216S500A	MR330	MR813
MPSA93	MR1120	MR331	MR814
MPSH10	MR1366	MR500	MR816
MPSL01	MR1376	MR5005	MR817
MPSL51	MR1386	MR501	MR818
MPSW01	MR1396	MR5010	MR820
MPSW01A	MR2400	MR502	MR821
MPSW06G	MR2400F	MR5020	MR822
MPSW06RLRAG	MR2401	MR5030	MR824
MPSW10	MR2401F	MR504	MR826
MPSW42	MR2402	MR5040	MR830
MPSW45G	MR2402F	MR5059	MR831
MPSW51	MR2404	MR506	MR832
MPSW51A	MR2404F	MR5060	MR834
MPSW51AG	MR2406	MR5061	MR836
MPSW51ARLRAG	MR2406F	MR508	MR850

Multisim 14.0 Power Pro Components

MR851	MRF9011L	MSQA6V1W5T2G	MTD20P03HDL
MR852	MRF9011LT1	MSR1560G	MTD2955E
MR854	MRF9011LT1_A	MSR860G	MTD2N50E
MR856	MRF9011LT1_B	MSRD620CTG	MTD3055V
MR860	MRF917T1	MSRD620CTRG	MTD3055VL
MR861	MRF927T1	MSRD620CTT4	MTD3N25E
MR862	MRF9331LT1	MSRD620CTT4G	MTD4N20E
MR864	MRF9411BL	MSRD620CTT4RG	MTD4P06
MR866	MRF9411L	MSRF1560G	MTD5N06
MR870	MRF9411LT1	MSRF860G	MTD5P06V
MR871	MRF947	MSS1P3LHM3/89A	MTD6N15T4G
MR872	MRF947T1	MSS1P4HM3/89A	MTD6N20E
MR874	MRF949T1	MSS1P6HM3/89A	MTD6N20ET4G
MR876	MRF9511AL	MSS2P3HM3/89A	MTD6P10E
MRA4003T3G	MRF9511L	MT4C4ME8DJ-5	MTDF1N03HD
MRA4004T3G	MRF9511LT1	MTB20N20E	MTH13N50
MRA4005T1G	MRS1504T3G	MTB23P06V	MTH30N20
MRA4005T3G	MSB92T1G	MTB2P50E	MTH5N100
MRA4006T3G	MSD1328-RT1G	MTB50P03HDL	MTH8N60
MRA4007T3G	MSD602-RT1G	MTB50P03HDLT4G	MTM10N100E
MRF5211LT1	MSE1PJHM3/89A	MTD10P06HDL	MTM15N20
MRF5711L	MSP3V3HM3/89A	MTD15N06V	MTM15N40
MRF5711LT1	MSP430P325IFN	MTD1N60E	MTM24N50E
MRF5812	MSP430P325IPG	MTD1N80E	MTM26N40E
MRF8372	MSP430P325IPM	MTD20N06HD	MTM2N85

Multisim 14.0 Power Pro Components

MTM2N90	MTP2N20	MTP8N20	MUN2216T1G
MTM2P45	MTP2N50	MTP8N50	MUN2230T1G
MTM40N20	MTP2N85	MTP8N50E	MUN2232T1G
MTM5N40	MTP2N90	MTP8P08	MUN2233T1G
MTM5P25	MTP2P45	MTP8P10	MUN2234T1G
MTM7N50	MTP2P50	MTP8P25	MUN2236T1G
MTM8N60	MTP2P50EG	MTSF3N02HD	MUN2237T1G
MTM8P08	MTP3055E/MC	MULTIPLIER	MUN2238T1G
MTM8P10	MTP3055V	MUN2111T1G	MUN2240T1G
MTP10N05E/MC	MTP3055VL	MUN2112T1G	MUN5111DW1T1G
MTP10N10M	MTP30N05E	MUN2113T1G	MUN5111T1G
MTP10N15	MTP30N08M	MUN2114T1G	MUN5112DW1T1G
MTP12P05	MTP35N06E	MUN2115T1G	MUN5112T1G
MTP12P06	MTP3N100	MUN2135T1G	MUN5113DW1T1G
MTP12P10	MTP40N06M	MUN2138T1G	MUN5113T1G
MTP15N05E	MTP4N50	MUN2141T1G	MUN5113T3G
MTP15N05L	MTP4N85	MUN2211T1	MUN5114DW1T1G
MTP15N06E	MTP50N05E	MUN2211T1G	MUN5114T1G
MTP15N08L	MTP50N05EL	MUN2211T3G	MUN5115DW1T1G
MTP15N15	MTP50N06E	MUN2212T1G	MUN5115T1G
MTP1N60	MTP5N20	MUN2213T1	MUN5116DW1T1G
MTP20P06	MTP6N60	MUN2213T1G	MUN5131T1G
MTP25N06	MTP6N60/MC	MUN2214T1G	MUN5132T1G
MTP25N06L	MTP75N05C	MUN2214T3G	MUN5133DW1T1G
MTP25N10E	MTP7N20	MUN2215T1G	MUN5133T1G

Multisim 14.0 Power Pro Components

MUN5135DW1T1G	MUN5240T1G	MUR110G	MUR1605CT
MUN5135T1G	MUN5241T1G	MUR110RLG	MUR160G
MUN5140T1G	MUN5311DW1T1G	MUR115	MUR160RLG
MUN5211DW1T1G	MUN5312DW1T1G	MUR115G	MUR1610CT
MUN5211T1	MUN5312DW1T2G	MUR115RLG	MUR1610CTG
MUN5211T1G	MUN5313DW1T1G	MUR120G	MUR1615CT
MUN5212DW1T1G	MUN5314DW1T1G	MUR120RLG	MUR1615CTG
MUN5212T1G	MUN5315DW1T1G	MUR130G	MUR1620CT
MUN5213DW1T1G	MUN5316DW1T1G	MUR130RLG	MUR1620CTG
MUN5213DW1T3G	MUN5330DW1T1G	MUR140G	MUR1620CTRG
MUN5213T1G	MUN5333DW1T1G	MUR140RLG	MUR1640CTG
MUN5214DW1T1G	MUN5334DW1T1G	MUR1505	MUR1660CTG
MUN5214T1G	MUN5335DW1T1G	MUR1510	MUR180EG
MUN5215DW1T1G	MUN5336DW1T1G	MUR1510G	MUR180ERLG
MUN5215T1G	MUR10005CT	MUR1515	MUR2020RG
MUN5216DW1T1G	MUR10010CT	MUR1515G	MUR2100EG
MUN5230DW1T1G	MUR10015CT	MUR1520	MUR2100ERLG
MUN5230T1G	MUR10020CT	MUR1520G	MUR210G
MUN5232DW1T1G	MUR10150E	MUR1530	MUR210RLG
MUN5232T1G	MUR105	MUR1540	MUR220G
MUN5233DW1T1G	MUR105G	MUR1540G	MUR220RLG
MUN5233T1G	MUR105RLG	MUR1550	MUR240G
MUN5235DW1T1G	MUR110	MUR1560	MUR240RLG
MUN5237DW1T1G	MUR1100EG	MUR1560G	MUR2505
MUN5238T1G	MUR1100ERLG	MUR160	MUR2510

Multisim 14.0 Power Pro Components

MUR2515	MUR420RLG	MUR820	MURA220T3G
MUR2520	MUR440G	MUR820G	MURA230T3G
MUR260G	MUR440RLG	MUR830	MURA240T3G
MUR260RLG	MUR460G	MUR840	MURB1620CTG
MUR3005PT	MUR460RLG	MUR840G	MURB1620CTRG
MUR3010PT	MUR480EG	MUR850	MURB1620CTRT4G
MUR3015PT	MUR480ERLG	MUR860	MURB1620CTT4
MUR3020PT	MUR5005	MUR860G	MURB1620CTT4G
MUR3020PTG	MUR5010	MUR880EG	MURB1660CTG
MUR3020WTG	MUR5015	MURA105T3G	MURB1660CTT4G
MUR3040PTG	MUR5020	MURA110T3	MURD320T4
MUR3060PTG	MUR550APFRLG	MURA110T3G	MURD320T4G
MUR3060WTG	MUR550PFG	MURA115T3G	MURD330T4G
MUR405	MUR605CT	MURA120T3	MURD340T4G
MUR405G	MUR610CT	MURA120T3G	MURD530T4G
MUR410	MUR615CT	MURA130T3G	MURD550PFT4G
MUR4100EG	MUR620CT	MURA140T3	MURD620CT
MUR4100ERLG	MUR620CTG	MURA140T3G	MURD620CTG
MUR410G	MUR805	MURA160T3	MURD620CTT4
MUR410RLG	MUR805G	MURA160T3G	MURD620CTT4G
MUR415	MUR810	MURA205T3G	MURF1560G
MUR415G	MUR8100EG	MURA210T3G	MURF1620CTG
MUR415RLG	MUR810G	MURA215T3	MURF1660CTG
MUR420	MUR815	MURA215T3G	MURF550PFG
MUR420G	MUR815G	MURA220T3	MURF860G

Multisim 14.0 Power Pro Components

MURH840CTG	MURS220T3G	MUX8_1	MZ5520B
MURH860CTG	MURS230T3	MV209	MZ5521B
MURHB840CTG	MURS230T3G	MVGSF1N03LT1G	MZ5522B
MURHB840CTT4	MURS240T3G	MVMBF0201NLT1G	MZ5523B
MURHB840CTT4G	MURS310T3	myRIO_MXP	MZ5524B
MURHB860CTT4G	MURS320T3	MZ4099	MZ5525B
MURHD560T4G	MURS320T3G	MZ4100	MZ5526B
MURHD560W1T4G	MURS340T3	MZ4101	MZ5527B
MURHF860CTG	MURS340T3G	MZ4102	MZ5528B
MURHS160T3G	MURS360BT3G	MZ4103	MZ5529B
MURS105T3G	MURS360-E3/57T	MZ4104	MZ5530B
MURS110T3	MURS360T3	MZ4614	MZPY10
MURS110T3G	MURS360T3G	MZ4615	MZPY100
MURS115T3	MURS480ET3G	MZ4616	MZPY11
MURS115T3G	MUSHROOM_HEAD	MZ4617	MZPY12
MURS120T3	MUX_16TO1	MZ4618	MZPY13
MURS120T3G	MUX_2TO1	MZ4619	MZPY15
MURS140T3	MUX_4TO1	MZ4620	MZPY16
MURS140T3G	MUX_8TO1	MZ4621	MZPY18
MURS160-E3/52T	MUX_LATCH	MZ4622	MZPY20
MURS160T3	MUX2_1	MZ4623	MZPY22
MURS160T3G	MUX2_1_INV	MZ4624	MZPY24
MURS205T3G	MUX2_1INV_3S	MZ4625	MZPY27
MURS210T3G	MUX4_1	MZ4626	MZPY3.9
MURS220T3	MUX4_1_INVO	MZ4627	MZPY30

Multisim 14.0 Power Pro Components

MZPY33	N83C196KB	NC7S00_5V	NC7S86_5V
MZPY36	N87C196KB	NC7S00_6V	NC7S86_6V
MZPY39	NAND13	NC7S02_2V	NC7ST00_5V
MZPY4.3	NAND2	NC7S02_3V	NC7ST02_5V
MZPY4.7	NAND2	NC7S02_4V	NC7ST04_5V
MZPY43	NAND3	NC7S02_5V	NC7ST08_5V
MZPY47	NAND3	NC7S02_6V	NC7ST32_5V
MZPY5.1	NAND4	NC7S04_2V	NC7ST86_5V
MZPY5.6	NAND4	NC7S04_3V	NC7SU04_2V
MZPY51	NAND5	NC7S04_4V	NC7SU04_3V
MZPY56	NAND5	NC7S04_5V	NC7SU04_4V
MZPY6.2	NAND6	NC7S04_6V	NC7SU04_5V
MZPY6.8	NAND6	NC7S08_2V	NC7SU04_6V
MZPY62	NAND7	NC7S08_3V	NC7SZ00_2V
MZPY68	NAND7	NC7S08_4V	NC7SZ00_3V
MZPY7.5	NAND8	NC7S08_5V	NC7SZ00_4V
MZPY75	NAND8	NC7S08_6V	NC7SZ00_5V
MZPY8.2	NBRB8H100T4G	NC7S32_2V	NC7SZ02_2V
MZPY82	NBRD5H100T4G	NC7S32_3V	NC7SZ02_3V
MZPY9.1	NBR52H100T3G	NC7S32_4V	NC7SZ02_4V
MZPY91	NC_CONTACT	NC7S32_5V	NC7SZ02_5V
N2550-6002RB	NC_RELAY_RATED	NC7S32_6V	NC7SZ04_2V
N74F545D	NC7S00_2V	NC7S86_2V	NC7SZ04_3V
N74F545N	NC7S00_3V	NC7S86_3V	NC7SZ04_4V
N80C196KB	NC7S00_4V	NC7S86_4V	NC7SZ04_5V

Multisim 14.0 Power Pro Components

NC7SZ05_2V	NC7SZ86_3V	NCP1012APL065R2 G	NCP1028PL100R2G
NC7SZ05_3V	NC7SZ86_4V	NCP1012APL100R2 G	NCP1030DMR2G
NC7SZ05_4V	NC7SZ86_5V	NCP1012APL130R2 G	NCP1031DR2G
NC7SZ05_5V	NC7SZU04_2V	NCP1012APL130R2 G	NCP1031MNTXG
NC7SZ08_2V	NC7SZU04_3V	NCP1012ST100T3G	NCP1050P100G
NC7SZ08_3V	NC7SZU04_4V	NCP1012ST130T3G	NCP1050P136G
NC7SZ08_4V	NC7SZU04_5V	NCP1012ST65T3G	NCP1050P44G
NC7SZ08_5V	NCP1010AP065G	NCP1013AP065G	NCP1050ST100T3G
NC7SZ125_2V	NCP1010AP100G	NCP1013AP100G	NCP1050ST136T3G
NC7SZ125_3V	NCP1010AP130G	NCP1013AP133G	NCP1050ST44T3G
NC7SZ125_4V	NCP1010ST100T3G	NCP1013ST100T3G	NCP1051P100G
NC7SZ125_5V	NCP1010ST130T3G	NCP1013ST130T3G	NCP1051P136G
NC7SZ126_2V	NCP1011AP065G	NCP1013ST65T3G	NCP1051P44G
NC7SZ126_3V	NCP1011AP100G	NCP1014AP065G	NCP1051ST100T3G
NC7SZ126_4V	NCP1011AP130G	NCP1014AP100G	NCP1051ST136T3G
NC7SZ126_5V	NCP1011APL065R2 G	NCP1014APL065R2 G	NCP1051ST44T3G
NC7SZ32_2V	NCP1011APL130R2 G	NCP1014APL100R2 G	NCP1052P100G
NC7SZ32_3V	NCP1011ST100T3G	NCP1014ST100T3G	NCP1052P136G
NC7SZ32_4V	NCP1011ST130T3G	NCP1014ST65T3G	NCP1052P44G
NC7SZ32_5V	NCP1012AP065G	NCP1027P065G	NCP1052ST100T3G
NC7SZ38_2V	NCP1012AP100G	NCP1027P100G	NCP1052ST136T3G
NC7SZ38_3V	NCP1012AP133G	NCP1028P065G	NCP1052ST44T3G
NC7SZ38_4V		NCP1028P100G	NCP1053P100G
NC7SZ38_5V			NCP1053P136G
NC7SZ86_2V			NCP1053P44G

Multisim 14.0 Power Pro Components

NCP1053ST100T3G	NCP1117DT25RKG	NCP1200P40G	NCP1217AD65R2G
NCP1053ST136T3G	NCP1117DT25T5G	NCP1200P60G	NCP1217AP100G
NCP1053ST44T3G	NCP1117DT285G	NCP1203D100R2G	NCP1217AP133G
NCP1054P100G	NCP1117DT285RKG	NCP1203D40R2G	NCP1217AP65G
NCP1054P136G	NCP1117DT33G	NCP1203D60R2G	NCP1217D100R2G
NCP1054P44G	NCP1117DT33RKG	NCP1203P100G	NCP1217D133R2G
NCP1054ST100T3G	NCP1117DT33T5G	NCP1203P40G	NCP1217D65R2G
NCP1054ST136T3G	NCP1117DT50G	NCP1203P60G	NCP1217P100G
NCP1054ST44T3G	NCP1117DT50RKG	NCP1207ADR2G	NCP1217P133G
NCP1055P100G	NCP1117DTAG	NCP1207APG	NCP1217P65G
NCP1055P136G	NCP1117DTARKG	NCP1207BDR2G	NCP1230D100R2G
NCP1055P44G	NCP1117DTAT5G	NCP1216AD100R2G	NCP1230D133R2G
NCP1055ST100T3G	NCP1117ST12T3G	NCP1216AD133R2G	NCP1230D165R2G
NCP1055ST136T3G	NCP1117ST15T3G	NCP1216AD65R2G	NCP1230D65R2G
NCP1055ST44T3G	NCP1117ST18T3G	NCP1216AP100G	NCP1230P100G
NCP1117DT12G	NCP1117ST20T3G	NCP1216AP133G	NCP1230P133G
NCP1117DT12RKG	NCP1117ST25T3G	NCP1216AP65G	NCP1230P65G
NCP1117DT15G	NCP1117ST285T3G	NCP1216D100R2G	NCP1271D100R2G
NCP1117DT15RKG	NCP1117ST33T3G	NCP1216D133R2G	NCP1271D65R2G
NCP1117DT18G	NCP1117ST50T3G	NCP1216D65R2G	NCP1271P100G
NCP1117DT18RKG	NCP1117STAT3G	NCP1216P100G	NCP1271P65G
NCP1117DT18T5G	NCP1200D100R2G	NCP1216P133G	NCP1308DR2G
NCP1117DT20G	NCP1200D40R2G	NCP1216P65G	NCP1337DR2G
NCP1117DT20RKG	NCP1200D60R2G	NCP1217AD100R2G	NCP1337PG
NCP1117DT25G	NCP1200P100G	NCP1217AD133R2G	NCP1338DR2G

Multisim 14.0 Power Pro Components

NCP1351ADR2G	NCP511SN25T1G	NCS2202SQ2T2G	NCV2904DMR2G
NCP1351APG	NCP511SN27T1G	NCV1117DT15RKG	NCV2904DR2G
NCP1351BDR2G	NCP511SN28T1G	NCV1117DT18RKG	NCV33063AVDR2G
NCP1351BPG	NCP511SN30T1G	NCV1117DT18T5G	NCV33074ADTBR2G
NCP1351CDR2G	NCP511SN33T1G	NCV1117DT20RKG	NCV33074DR2G
NCP1351CPG	NCP511SN50T1G	NCV1117DT25RKG	NCV33272ADR2G
NCP1351DDR2G	NCP5208DR2G	NCV1117DT33T5G	NCV833DR2G
NCP1351DPG	NCP5217AMNTXG	NCV1117DT50RKG	NDD01N60-1G
NCP1377BD1R2G	NCP5355D	NCV1117DTARKG	NDD01N60T4G
NCP1377BDR2G	NCP5355DG	NCV1117ST12T3G	NDD02N40-1G
NCP1377BPG	NCP5355PDR2	NCV1117ST15T3G	NDD02N40T4G
NCP1377D1R2G	NCP6334BMTAATBG	NCV1117ST18T3G	NDD02N60Z-1G
NCP1377DR2G	NCP6334CMTAATBG	NCV1117ST20T3G	NDD02N60ZT4G
NCP1377PG		NCV1117ST25T3G	NDD03N50Z-1G
NCP1410DMR2G	NCS2001SN1T1G	NCV1117ST33T3G	NDD03N50ZT4G
NCP2809ADMR2G	NCS2001SN2T1G	NCV1117ST50T3G	NDD03N60Z-1G
NCP2809BDMR2G	NCS2001SQ1T2G	NCV1117STAT3G	NDD03N60ZT4G
NCP2809BMUTXG	NCS2001SQ2T2G	NCV2001SN2T1G	NDD03N80Z-1G
NCP2890AFCT2G	NCS2200SN1T1G	NCV2001SQ2T2G	NDD03N80ZT4G
NCP2890DMR2G	NCS2200SN2T1G	NCV2901DR2G	NDD04N50Z-1G
NCP4894DMR2G	NCS2200SQ2T2G	NCV2901DTBR2G	NDD04N50ZT4G
NCP4894FCT1G	NCS2200SQLT1G	NCV2902DR2G	NDD04N60Z-1G
NCP4894MNR2G	NCS2202SN1T1G	NCV2902DTBR2G	NDD04N60ZT4G
NCP511SN15T1G	NCS2202SN2T1G	NCV2903DMR2G	NDD05N50Z-1G
NCP511SN18T1G	NCS2202SQ1T2G	NCV2903DR2G	

Multisim 14.0 Power Pro Components

NDD05N50ZT4G	NDF9406	NE5532IP	NGD8201NT4G
NDD60N360U1-1G	NDF9407	NE5532P	NGTB15N60S1EG
NDD60N360U1-35G	NDF9409	NE5534AD	NGTB50N60FLWG
NDD60N360U1T4G	NDF9410	NE5534AP	NHPJ08S600G
NDF02N60ZG	NDS8852H	NE5534D	NHPJ15S600G
NDF02N60ZH	NDS8858H	NE5534P	NHPV08S600G
NDF03N60ZG	NDS8936	NET_10	NHPV15S600G
NDF03N60ZH	NDS8947	NET_12	NI_2VHDCI_68_68_ RA
NDF04N60ZG	NDS9936	NET_14	NI_50MIL_68_RA
NDF04N60ZH	NDS9942	NET_16	NI_50MIL_68_V
NDF04N62ZG	NDS9943	NET_18	NI_cRIO_4LED_RA
NDF05N50ZG	NDS9947	NET_2	NI_cRIO_BNC
NDF05N50ZH	NDS9948	NET_20	NI_cRIO_DSUB25M
NDF06N60ZG	NDS9952	NET_3	NI_cRIO_DSUB37M
NDF06N60ZH	NDS9952A	NET_4	NI_cRIO_INTERFAC E_GENERIC
NDF06N62ZG	NDS9953	NET_6	NI_cRIO_INTERFAC E_ID
NDF08N50ZG	NDS9953A	NET_8	NI_cRIO_INTERFAC E_PARALLEL
NDF08N50ZH	NDS9955	NF5101	NI_cRIO_INTERFAC E_SPI
NDF08N60ZG	NDS9956A	NF5102	NI_cRIO_INTERFAC E_USER
NDF08N60ZH	NDS9958	NF5103	NI_cRIO_SCREWTE RM10
NDF10N60ZG	NDS9959	NF5301	NI_sbRIO_J5_CONN
NDF10N60ZH	NDT01N60T1G	NGB18N40CLBT4G	
NDF10N62ZG	NE5532AI	NGB8207NT4G	
NDF11N50ZG	NE5532AIP	NGD15N41CLT4G	
NDF11N50ZH	NE5532AP	NGD18N40CLBT4G	

Multisim 14.0 Power Pro Components

NI_sbRIO_J6_CONN	NI-	NI-PCI-6014	NI-PCI-6225
NI_sbRIO_J7_CONN	9683_HALFBRIDGE_DO	NI-PCI-6023E	NI-PCI-6229
NI_sbRIO_J7_PORTS	NI-9683_LVTTL	NI-PCI-6024E	NI-PCI-6230
NI_sbRIO_P2_CONN	NI-AT-GPIB/TNT	NI-PCI-6030E	NI-PCI-6232
	NID9N05CLT4G	NI-PCI-6032E	NI-PCI-6233
NI_sbRIO_P2_PORTS	NI-DAQCard-6024E	NI-PCI-6034E	NI-PCI-6236
	NI-DAQCard-6036E	NI-PCI-6035E	NI-PCI-6238
NI_sbRIO_P3_CONN	NI-DAQCard-6062E	NI-PCI-6036E	NI-PCI-6239
	NI-DAQPad-	NI-PCI-6040E	NI-PCI-6250
NI_sbRIO_P3_PORTS	6015(Mass.Term.)	NI-PCI-6052E	NI-PCI-6254
NI_sbRIO_P4_CONN	NI-DAQPad-6020E	NI-PCI-6070E	NI-PCI-6255
	NI-DAQPad-6052E	NI-PCI-6110	NI-PCI-6259
NI_sbRIO_P4_PORTS	NI-ExpressCard-GPIB	NI-PCI-6111	NI-PCI-6280
NI_sbRIO_P5_CONN	NIF9N05CLT1G	NI-PCI-6115	NI-PCI-6281
	NIF9N05CLT3G	NI-PCI-6120	NI-PCI-6284
NI_sbRIO_P5_PORTS	NI-GPIB-ENET/100	NI-PCI-6122	NI-PCI-6289
NI_VHDCI_68_RA	NI-GPIB-ENET/1000	NI-PCI-6123	NI-PCI-7811R
NI_VHDCI_68_V	NI-GPIB-PCII/IIA	NI-PCI-6132	NI-PCI-7813R
NI-78xxR_RDIO	NI-GPIB-RS232	NI-PCI-6133	NI-PCI-
NI-9683_AI	NI-GPIB-RS485/422	NI-PCI-6143	7830R_RMIO
NI-9683_AIO	NI-GPIB-USB-HS	NI-PCI-6154	NI-PCI-
NI-9683_DI	NI-myDAQ	NI-PCI-6220	7831R_RMIO
NI-9683_DO	NI-PCI-6011E	NI-PCI-6221	NI-PCI-
	NI-PCI-6013	NI-PCI-6221(37-Pin)	7833R_RMIO
		NI-PCI-6224	NI-PCI-8232
			NI-PCIe-6251

Multisim 14.0 Power Pro Components

NI-PCle-6259	NI-PMC-GPIB	NI-PXI-6255	NI-PXIe-6368
NI-PCle-6320	NI-PXI-6030E	NI-PXI-6259	NI-PXI-GPIB
NI-PCle-6321	NI-PXI-6040E	NI-PXI-6280	NI-sbRIO-9605
NI-PCle-6323	NI-PXI-6052E	NI-PXI-6281	NI-sbRIO-9606
NI-PCle-6341	NI-PXI-6070E	NI-PXI-6284	NI-sbRIO-9651
NI-PCle-6343	NI-PXI-6115	NI-PXI-6289	NI-SCXI-1127_1-Wire
NI-PCle-6351	NI-PXI-6120	NI-PXI-7811R	NI-SCXI-1127_2-Wire
NI-PCle-6353	NI-PXI-6122	NI-PXI-7813R	NI-SCXI-1127_4-Wire
NI-PCle-6361	NI-PXI-6123	NI-PXI-7830R_RMIO	NI-SCXI-1127_Independent
NI-PCle-6363	NI-PXI-6132	NI-PXI-7831R_RMIO	NI-SCXI-1127_Matrix
NI-PCle-7841R_RMIO	NI-PXI-6133	NI-PXI-7833R_RMIO	NI-SCXI-1128_1-Wire
NI-PCle-7842R_RMIO	NI-PXI-6143	NI-PXI-7841R_RMIO	NI-SCXI-1128_2-Wire
NI-PCle-7851R_RMIO	NI-PXI-6221	NI-PXI-7842R_RMIO	NI-SCXI-1128_4-Wire
NI-PCle-7852R_RMIO	NI-PXI-6224	NI-PXI-7851R_RMIO	NI-SCXI-1128_Independent
NI-PCle-GPIB	NI-PXI-6225	NI-PXI-7852R_RMIO	NI-SCXI-1128_Matrix
NI-PCle-GPIB/LP	NI-PXI-6229	NI-PXI-7853R_RMIO	NI-SCXI-1160
NI-PCle-GPIB+	NI-PXI-6230	NI-PXI-7854R_RMIO	NI-SCXI-1163R
NI-PCle-GPIB+/LP	NI-PXI-6232	NI-PXI-8232	NI-USB-6212(Mass.Term.)
NI-PCI-GPIB	NI-PXI-6233	NI-PXIe-6124	
NI-PCI-GPIB/LP	NI-PXI-6236	NI-PXIe-6341	
NI-PCI-GPIB+	NI-PXI-6238	NI-PXIe-6356	
NI-PCMCIA-GPIB	NI-PXI-6239	NI-PXIe-6358	
	NI-PXI-6250	NI-PXIe-6361	
	NI-PXI-6251	NI-PXIe-6363	
	NI-PXI-6254	NI-PXIe-6366	

Multisim 14.0 Power Pro Components

NI-USB- 6216(Mass.Term.)	NJL3281DG	NJM074D	NJM2058D
	NJL4281D	NJM074M	NJM2058M
NI-USB- 6225(Mass.Term.)	NJL4281DG	NJM074V	NJM2059D
	NJL4302D	NJM082BD	NJM2059M
NI-USB- 6251(Mass.Term.)	NJL4302DG	NJM082BL	NJM2060D
	NJM022BD	NJM082BM	NJM2060M
	NJM022BL	NJM082BV	NJM2068D
NI-USB- 6259(Mass.Term.)	NJM022BM	NJM082D	NJM2068L
	NJM022D	NJM082L	NJM2068M
NI-USB- 6281(Mass.Term.)	NJM022L	NJM082V	NJM2082D
	NJM022M	NJM084D	NJM2082L
NI-USB-7845R_MIO	NJM062D	NJM084M	NJM2082M
NI-USB-7846R_MIO	NJM062L	NJM084V	NJM2097M
NI-USB-7855R_MIO	NJM062M	NJM13600D	NJM2100D
NI-USB-7856R_MIO	NJM062V	NJM13600M	NJM2100L
NI-USB-78xxR_DIO	NJM064D	NJM13700D	NJM2100M
	NJM064M	NJM13700M	NJM2100V
NJD1718T4G	NJM064V	NJM1458D	NJM2107F
NJD2873T4G	NJM072BD	NJM1458M	NJM2114D
NJD35N04G	NJM072BL	NJM2041D	NJM2114L
NJD35N04T4G	NJM072BM	NJM2041L	NJM2115D
NJL0281D	NJM072BV	NJM2041M	NJM2115L
NJL0281DG	NJM072D	NJM2043D	NJM2115M
NJL0302D	NJM072L	NJM2043L	NJM2120D
NJL0302DG	NJM072M	NJM2043M	NJM2120L
NJL1302DG			

Multisim 14.0 Power Pro Components

NJM2120M	NJM3414M	NJM741D	NJVMJD32CG
NJM2121D	NJM3415D	NJM741E	NJVMJD32CT4G
NJM2121L	NJM3415L	NJM741M	NJVMJD32T4G
NJM2121M	NJM3415M	NJMOP-07D	NJVMJD350T4G
NJM2900M	NJM3416V	NJMOP-07M	NJVMJD42CRLG
NJM2900N	NJM353D	NJT4030PT1G	NJVMJD42CT4G
NJM2902M	NJM353M	NJT4030PT3G	NJVMJD44E3T4G
NJM2902N	NJM3900M	NJT4031NT1G	NJVMJD44H11G
NJM2902V	NJM3900N	NJT4031NT3G	NJVMJD44H11RLG
NJM2904D	NJM4250D	NJV4030PT1G	NJVMJD44H11T4G
NJM2904L	NJM4250M	NJV4030PT3G	NJVMJD45H11RLG
NJM2904M	NJM4565D	NJV4031NT1G	NJVMJD45H11T4G
NJM2904V	NJM4565L	NJV4031NT3G	NJVMJD50T4G
NJM318D	NJM4565M	NJVMJB41CT4G	NJVMJD6039T4G
NJM318M	NJM4565V	NJVMJB42CT4G	NJVNJD2873T4G
NJM324D	NJM4580D	NJVMJB44H11T4G	NJVNJD35N04G
NJM324M	NJM4580E	NJVMJB45H11T4G	NJVNJD35N04T4G
NJM3403AD	NJM4580L	NJVMJD112T4G	NJW0281G
NJM3403AM	NJM4741D	NJVMJD117T4G	NJW0302G
NJM3403AV	NJM4741M	NJVMJD210T4G	NJW1302G
NJM3404AD	NJM5532D	NJVMJD243T4G	NJW21193G
NJM3404AL	NJM5532L	NJVMJD253T4G	NJW21194G
NJM3404AM	NJM5532M	NJVMJD2955T4G	NJW3281G
NJM3414D	NJM5534D	NJVMJD3055T4G	NJX1675PDR2G
NJM3414L	NJM5534M	NJVMJD31T4G	NLT_VIRTUAL

Multisim 14.0 Power Pro Components

NMOSFET_Thermal	NOR8	NRVB140ESFT1G	NRVB560MFST3G
NO_CONTACT	NOR8	NRVB140ESFT3G	NRVB5H100MFST1G
NO_RELAY_RATED	NOT	NRVB140SFT1G	NRVB8H100MFST1G
NON_IDEAL_BATTERY	NPD5564	NRVB140SFT3G	NRVB8H100MFST3G
NON_IDEAL_CAPACITOR	NPD5565	NRVB1H100SFT3G	NRVB8H100MFST3G
NON_IDEAL_CAPACITOR	NPD5566	NRVB2045EMFST1G	NRVBA130LT3G
NON_IDEAL_INDUC TOR	NPD8301	NRVB2045EMFST3G	NRVBA160T3G
NON_IDEAL_INDUC TOR	NPD8303	NRVB2H100SFT3G	NRVBA1H100T3G
NON_IDEAL_RESISTOR	NRVA4004T3G	NRVB2H100SFT3G	NRVBA210LT3G
NONC_RELAY_RATE D	NRVB0530T1G	NRVB30H100MFST1G	NRVBA2H100T3G
NONC_RELAY_RATE D	NRVB0530T3G	NRVB30H100MFST3G	NRVBA340T3G
NONLINEAR_DEPENDENT	NRVB0540T1G	NRVB30H100MFST3G	NRVBB1060T4G
NONLINEAR_DEPENDENT	NRVB0540T3G	NRVB440MFST1G	NRVBB20100CTT4G
NOR2	NRVB10100G	NRVB440MFST3G	NRVBB2060CTT4G
NOR2	NRVB10100MFST1G	NRVB440MFSWFT1G	NRVBB20H100CTT4G
NOR3	NRVB10100MFST3G	NRVB440MFSWFT3G	NRVBB2535CTLG
NOR3	NRVB10100MFST3G	NRVB460MFST1G	NRVBB2535CTLT4G
NOR4	NRVB1045MFST1G	NRVB460MFST3G	NRVBB3030CTLG
NOR4	NRVB1045MFST3G	NRVB5100MFST1G	NRVBB3030CTLT4G
NOR5	NRVB120ESFT1G	NRVB5100MFST3G	NRVBB30H60CTT4G
NOR5	NRVB120ESFT3G	NRVB540MFST1G	NRVBB4030T4G
NOR6	NRVB120LSFT1G	NRVB540MFST3G	NRVBB41H100CTT4G
NOR6	NRVB1240MFST1G	NRVB560MFST1G	
NOR7	NRVB1240MFST3G		
NOR7	NRVB130T1G		

Multisim 14.0 Power Pro Components

NRVBBS20100CTT4 G	NRVBS4201T3G	NSBA114TDP6T5G	NSBA144WDP6T5G
	NRVBS540T3G	NSBA114TF3T5G	NSBA144WF3T5G
NRVBD1035CTL4G	NRVS1504T3G	NSBA114YDP6T5G	NSBC113EF3T5G
NRVBD640CTG	NRVUB1620CTRT4G	NSBA114YDXV6T1G	NSBC114EDP6T5G
NRVBD640CTT4G	NRVUB1620CTT4G	NSBA115EDXV6T1G	NSBC114EDXV6T1G
NRVBD650CTT4G	NRVUB1660CTT4G	NSBA115TDP6T5G	NSBC114EDXV6T5G
NRVBD660CTG	NRVUD550PFT4G	NSBA115TF3T5G	NSBC114EF3T5G
NRVBD660CTT4G	NRVUD620CTG	NSBA123EF3T5G	NSBC114EPDP6T5G
NRVBM110ET1G	NRVUD620CTT4G	NSBA123JDP6T5G	NSBC114EPDXV6T1 G
NRVBM110LT1G	NRVUS230T3G	NSBA123JDXV6T5G	
NRVBM110LT3G	NRVUS240T3G	NSBA123JF3T5G	NSBC114EPDXV6T5 G
NRVBM120ET1G	NS32FV16-20	NSBA123TDP6T5G	NSBC114TDP6T5G
NRVBM120ET3G	NS32FV16-25	NSBA123TF3T5G	NSBC114TDXV6T1G
NRVBM130LT1G	NS32FX161-15	NSBA124EDP6T5G	NSBC114TF3T5G
NRVBM130LT3G	NS32FX161-20	NSBA124EF3T5G	NSBC114YDP6T5G
NRVBM140T1G	NS32FX164-20	NSBA124XF3T5G	NSBC114YDXV6T1G
NRVBM140T3G	NS32FX164-25	NSBA143EDP6T5G	NSBC114YDXV6T5G
NRVBS2040LT3G	NSA5.0AT3G	NSBA143EF3T5G	NSBC114YF3T5G
NRVBS240LT3G	NSB12ANT3G	NSBA143TF3T5G	NSBC114YPDP6T5G
NRVBS260T3G	NSB4904DW1T1G	NSBA143ZDP6T5G	NSBC114YPDXXV6T1 G
NRVBS3100T3G	NSB8MT-E3/81	NSBA143ZF3T5G	
NRVBS3200T3G	NSB9435T1G	NSBA144EDP6T5G	NSBC114YPDXXV6T5 G
NRVBS3201T3G	NSBA114EDP6T5G	NSBA144EDXV6T1G	NSBC115EDXV6T1G
NRVBS330T3G	NSBA114EDXV6T1G	NSBA144EF3T5G	
NRVBS360T3G	NSBA114EF3T5G	NSBA144TF3T5G	NSBC115TDP6T5G

Multisim 14.0 Power Pro Components

NSBC115TF3T5G	NSBC143ZPDXV6T1 G	NSI45030T1G	NSR0240V2T1G
NSBC115TPDP6T5G	NSBC144EDP6T5G	NSI45030ZT1G	NSR02F30NXT5G
NSBC123EF3T5G	NSBC144EDXV6T1G	NSI45035JZT1G	NSR02L30NXT5G
NSBC123JDP6T5G	NSBC144EDXV6T5G	NSI45060DDT4G	NSR0320MW2T1G
NSBC123JF3T5G	NSBC144EF3T5G	NSI45090DDT4G	NSR0320MW2T3G
NSBC123JPDP6T5G	NSBC144EPDP6T5G	NSI45090JDT4G	NSR0320XV6T1G
NSBC123JPDXV6T1 G	NSBC144EPDXV6T1 G	NSI50010YT1G	NSR0320XV6T5G
NSBC123TDP6T5G	NSBC144TF3T5G	NSI50150ADT4G	NSR0340HT1G
NSBC123TF3T5G	NSBC144WDP6T5G	NSI50350ADT4G	NSR0340P2T5G
NSBC124EDP6T5G	NSBC144WF3T5G	NSI50350AST3G	NSR0340V2T1G
NSBC124EDXV6T1G	NSD16F3T5G	NSIC2020BT3G	NSR0520V2T1G
NSBC124EF3T5G	NSD914F3T5G	NSIC2030BT3G	NSR05F20NXT5G
NSBC124EPDXV6T1 G	NSDEMP11XV6T1G	NSIC2050BT3G	NSR05F30NXT5G
NSBC124XF3T5G	NSDEMP11XV6T5G	NSL12AWT1G	NSR05F40NXT5G
NSBC143EDP6T5G	NSI45015WT1G	NSM80100MT1G	NSR0620P2T5G
NSBC143EF3T5G	NSI45020AT1G	NSM80101MT1G	NSR1020MW2T1G
NSBC143TF3T5G	NSI45020JZT1G	NSR0130P2T5G	NSR1020MW2T3G
NSBC143TPDXV6T1 G	NSI45020T1G	NSR0140P2T5G	NSR10F20NXT5G
NSBC143ZDP6T5G	NSI45025AT1G	NSR01F30MXT5G	NSR10F30NXT5G
NSBC143ZDXV6T1G	NSI45025AZT1G	NSR01F30NXT5G	NSR10F40NXT5G
NSBC143ZF3T5G	NSI45025T1G	NSR01L30MXT5G	NSR20F20NXT5G
NSBC143ZPDP6T5G	NSI45025ZT1G	NSR01L30NXT5G	NSR20F30NXT5G
	NSI45030AT1G	NSR0230P2T5G	NSR30CM3T5G
	NSI45030AZT1G	NSR0240HT1G	NSRLV20MW2T1G
		NSR0240P2T5G	NSS12100M3T5G

Multisim 14.0 Power Pro Components

NSS12100UW3TCG	NSS35200CF8T1G	NST3906F3T5G	NSVB123JPDXV6T1G
NSS12100XV6T1G	NSS35200MR6T1G	NST3946DXV6T1G	NSVB143ZPDXV6T1G
NSS12200LT1G	NSS40200LT1G	NST3946DXV6T5G	NSVB144EPDXV6T1G
NSS12200WT1G	NSS40200UW6T1G	NST846BF3T5G	NSVBA114YDXV6T1G
NSS12201LT1G	NSS40201LT1G	NST847BF3T5G	NSVBAT54WT1G
NSS12500UW3T2G	NSS40300DDR2G	NST848BF3T5G	NSVBAV70TT1G
NSS12501UW3T2G	NSS40300MDR2G	NST856BF3T5G	NSVBAV70TT3G
NSS12601CF8T1G	NSS40300MZ4T1G	NST857BF3T5G	NSVBC124EDXV6T1G
NSS1C200LT1G	NSS40301MDR2G	NSTB1005DXV5T1G	NSVBBCP69T1G
NSS1C200MZ4T1G	NSS40301MZ4T1G	NSTR4501NT1G	NSVMMBD353LT1G
NSS1C200MZ4T3G	NSS40302PDR2G	NSV1C300ET4G	NSVMMBT589LT1G
NSS1C201LT1G	NSS40500UW3T2G	NSV1C301ET4G	NSVMMBTH10LT1G
NSS1C201MZ4T1G	NSS40501UW3T2G	NSV20200LT1G	NSVMMUN2132LT1G
NSS1C201MZ4T3G	NSS40600CF8T1G	NSV20201LT1G	NSVMMUN2232LT1G
NSS1C300ET4G	NSS40601CF8T1G	NSV40200LT1G	NSVMUN2212T1G
NSS1C301ET4G	NSS60200LT1G	NSV40201LT1G	NSVMUN2233T1G
NSS20200LT1G	NSS60201LT1G	NSV40300MDR2G	NSVMUN5131T1G
NSS20201LT1G	NSS60600MZ4T1G	NSV40300MZ4T1G	NSVMUN5132T1G
NSS20300MR6T1G	NSS60601MZ4T1G	NSV40301MZ4T1G	NSVMUN5212DW1T1G
NSS20500UW3T2G	NST30010MXV6T1G	NSV60600MZ4T1G	
NSS20501UW3T2G	NST3904DXV6T1G	NSV60600MZ4T3G	
NSS20601CF8T1G	NST3904DXV6T5G	NSV60601MZ4T1G	
NSS30100LT1G	NST3904DXV6T5G	NSV60601MZ4T3G	
NSS30101LT1G	NST3904F3T5G	NSV9435T1G	
NSS30201MR6T1G	NST3906DXV6T1G		

Multisim 14.0 Power Pro Components

NSVMUN5333DW1 T1G	NTB6413ANG	NTD3055L104T4G	NTD4815NT4G
NSVMUN5334DW1 T1G	NTB6413ANT4G	NTD3055L170T4G	NTD4855NT4G
NSVT30010MXV6T1 G	NTB75N03L09T4G	NTD32N06LT4G	NTD4856NT4G
NSVT3904DXV6T1G	NTB75N06T4G	NTD40N03RT4G	NTD4857NT4G
	NTBV5605T4G	NTD4302T4G	NTD4858N-35G
	NTD110N02RT4G	NTD4804NT4G	NTD4858NT4G
NTA4001NT1G	NTD12N10-1G	NTD4805N-1G	NTD4860N-35G
NTA4151PT1G	NTD12N10T4G	NTD4805NT4G	NTD4860NT4G
NTA4153NT1G	NTD14N03RT4G	NTD4806N-35G	NTD4863N-35G
NTA7002NT1G	NTD18N06LT4G	NTD4806NT4G	NTD4863NAT4G
NTB25P06T4G	NTD18N06T4G	NTD4808N-1G	NTD4863NT4G
NTB30N06LT4G	NTD20N03L27T4G	NTD4808NT4G	NTD4863NT4H
NTB30N20T4G	NTD20N06T4G	NTD4809N-35G	NTD4865NT4G
NTB45N06LT4G	NTD20P06LG	NTD4809NH-1G	NTD4904N-1G
NTB45N06T4G	NTD20P06LT4G	NTD4809NH-35G	NTD4904N-35G
NTB5404NT4G	NTD24N06LT4G	NTD4809NHT4G	NTD4904NT4G
NTB5405NT4G	NTD24N06T4G	NTD4809NT4G	NTD4905N-1G
NTB5605PT4G	NTD2955-1G	NTD4810N-35G	NTD4905N-35G
NTB60N06T4G	NTD2955G	NTD4810NT4G	NTD4905NT4G
NTB6410ANG	NTD2955T4G	NTD4813N-35G	NTD4906N-1G
NTB6410ANT4G	NTD3055-094-1G	NTD4813NH-1G	NTD4906N-35G
NTB6411ANG	NTD3055-094T4G	NTD4813NH-35G	NTD4906NT4G
NTB6411ANT4G	NTD3055-150T4G	NTD4813NHT4G	NTD4909N-1G
NTB6412ANG	NTD3055L104-1G	NTD4813NT4G	NTD4909N-35G
NTB6412ANT4G	NTD3055L104G	NTD4815N-35G	NTD4909NT4G

Multisim 14.0 Power Pro Components

NTD4910N-1G	NTD5804NT4G	NTF3055-100T3G	NTHD4502NT1G
NTD4910N-35G	NTD5805NT4G	NTF3055L108T1G	NTHD4508NT1G
NTD4910NT4G	NTD5806NT4G	NTF3055L175T1G	NTHD4P02FT1G
NTD4913N-1G	NTD5807NT4G	NTF5P03T3G	NTHS4101PT1G
NTD4913N-35G	NTD5865NL-1G	NTF6P02T3G	NTHS4166NT1G
NTD4913NT4G	NTD5865NLT4G	NTGD1100LT1G	NTHS5404T1G
NTD4960N-1G	NTD5867NL-1G	NTGD3149CT1G	NTHS5441T1G
NTD4960N-35G	NTD5867NLT4G	NTGD4161PT1G	NTHS5443T1G
NTD4960NT4G	NTD6414AN-1G	NTGD4167CT1G	NTJD1155LT1G
NTD4963N-1G	NTD6414ANT4G	NTGS3130NT1G	NTJD4001NT1G
NTD4963N-35G	NTD6415AN-1G	NTGS3136PT1G	NTJD4105CT1G
NTD4963NT4G	NTD6415ANLT4G	NTGS3441PT1G	NTJD4105CT2G
NTD4965N-1G	NTD6415ANT4G	NTGS3441T1G	NTJD4152PT1G
NTD4965N-35G	NTD6416AN-1G	NTGS3443T1G	NTJD4158CT1G
NTD4965NT4G	NTD6416ANL-1G	NTGS3446T1G	NTJD4158CT2G
NTD4969N-1G	NTD6416ANLT4G	NTGS4111PT1G	NTJD4401NT1G
NTD4969N-35G	NTD6416ANT4G	NTGS4141NT1G	NTJD5121NT1G
NTD4969NT4G	NTD6600NT4G	NTGS5120PT1G	NTJD5121NT2G
NTD4970N-1G	NTD70N03R-1G	NTHC5513T1G	NTJS3151PT1G
NTD4970N-35G	NTD70N03RT4G	NTHD2102PT1G	NTJS3157NT1G
NTD4970NT4G	NTDV20N06T4G	NTHD3100CT1G	NTJS4151PT1G
NTD5406NT4G	NTE4151PT1G	NTHD3101FT1G	NTJS4160NT1G
NTD5407NT4G	NTE4153NT1G	NTHD3102CT1G	NTJS4405NT1G
NTD5802NT4G	NTF2955T1G	NTHD3133PFT1G	NTK3043NT1G
NTD5803NT4G	NTF3055-100T1G	NTHD4102PT1G	NTK3134NT1G

Multisim 14.0 Power Pro Components

NTK3134NT5G	NTMD3P03R2G	NTMFS4834NT1G	NTMFS4923NET1G
NTK3139PT1G	NTMD4184PFR2G	NTMFS4835NT1G	NTMFS4923NET3G
NTK3139PT5G	NTMD4820NR2G	NTMFS4836NT1G	NTMFS4925NET1G
NTK3142PT1G	NTMD4840NR2G	NTMFS4837NHT1G	NTMFS4925NET3G
NTLGD3502NT2G	NTMD4884NFR2G	NTMFS4839NHT1G	NTMFS4925NT1G
NTLGF3402PT2G	NTMD4N03R2G	NTMFS4841NHT1G	NTMFS4925NT3G
NTLJD3115PT1G	NTMD5836NLR2G	NTMFS4841NT1G	NTMFS4926NET1G
NTLJD3119CTAG	NTMD5838NLR2G	NTMFS4845NT1G	NTMFS4926NET3G
NTLJD3119CTBG	NTMD6N02R2G	NTMFS4846NT1G	NTMFS4926NT1G
NTLJD4116NT1G	NTMD6N04R2G	NTMFS4847NAT1G	NTMFS4926NT3G
NTLJF3117PT1G	NTMD6P02R2G	NTMFS4847NAT3G	NTMFS4927NT1G
NTLJF4156NT1G	NTMFD4901NFT1G	NTMFS4847NT1G	NTMFS4927NT3G
NTLJF4156NTAG	NTMFD4901NFT3G	NTMFS4851NT1G	NTMFS4931NT1G
NTLJS2103PTBG	NTMFD4902NFT1G	NTMFS4852NT1G	NTMFS4931NT3G
NTLJS3113PT1G	NTMFD4902NFT3G	NTMFS4852NT3G	NTMFS4934NT1G
NTLJS3113PTAG	NTMFS4108NT1G	NTMFS4897NFT1G	NTMFS4934NT3G
NTLJS4114NT1G	NTMFS4119NT1G	NTMFS4897NFT3G	NTMFS4935NT1G
NTLLD4901NFTWG	NTMFS4744NT1G	NTMFS4898NFT1G	NTMFS4935NT3G
NTLUD3A260PZTAG	NTMFS4821NT1G	NTMFS4898NFT3G	NTMFS4936NT1G
NTLUD3A260PZTBG	NTMFS4823NT1G	NTMFS4899NFT1G	NTMFS4936NT3G
NTLUF4189NZTAG	NTMFS4823NT3G	NTMFS4899NFT3G	NTMFS4937NT1G
NTLUS3A40PZTAG	NTMFS4825NFET1G	NTMFS4921NT1G	NTMFS4937NT3G
NTLUS3A40PZTBG	NTMFS4825NFET3G	NTMFS4921NT3G	NTMFS4939NT1G
NTLUS3A90PZTAG	NTMFS4833NT1G	NTMFS4922NET1G	NTMFS4939NT3G
NTLUS3A90PZTBG	NTMFS4833NT3G	NTMFS4922NET3G	NTMFS4941NT1G

Multisim 14.0 Power Pro Components

NTMFS4941NT3G	NTMS4935NR2G	NTS2101PT1G	NTST40120CTG
NTMFS4943NT1G	NTMS4937NR2G	NTS4001NT1G	NTST40120CTH
NTMFS4943NT3G	NTMS4939NR2G	NTS4101PT1G	NTSV20100CTG
NTMFS4945NT1G	NTMS5835NLR2G	NTS4173PT1G	NTSV20120CTG
NTMFS4983NFT1G	NTMS5838NLR2G	NTS4409NT1G	NTSV20U100CTG
NTMFS4983NFT3G	NTMS5P02R2G	NTSB20100CT-1G	NTSV30100CTG
NTMFS4985NFT1G	NTNS3A65PZT5G	NTSB20U100CT-1G	NTSV30120CTG
NTMFS4985NFT3G	NTNUS3171PZT5G	NTSB30100CT-1G	NTTD4401FR2G
NTMFS5830NLT1G	NTP2955G	NTSB30100S-1G	NTTFS4800NTAG
NTMFS5832NLT1G	NTP35N15G	NTSB30U100CT-1G	NTTFS4821NTAG
NTMS10P02R2G	NTR0202PLT1G	NTSJ20100CTG	NTTFS4821NTWG
NTMS4176PR2G	NTR1P02LT1G	NTSJ2080CTG	NTTFS4823NTAG
NTMS4177PR2G	NTR1P02LT3G	NTSJ20U100CTG	NTTFS4823NTWG
NTMS4503NR2G	NTR2101PT1G	NTSJ30100CTG	NTTFS4824NTAG
NTMS4800NR2G	NTR3161NT1G	NTSJ3080CTG	NTTFS4840NTAG
NTMS4801NR2G	NTR3162PT1G	NTSJ30U80CTG	NTTFS4929NTAG
NTMS4802NR2G	NTR4003NT1G	NTST20100CTG	NTTFS4929NTWG
NTMS4807NR2G	NTR4003NT3G	NTST20120CTG	NTTFS4932NTAG
NTMS4816NR2G	NTR4101PT1G	NTST20U100CTG	NTTFS4932NTWG
NTMS4840NR2G	NTR4170NT1G	NTST30100CTG	NTTFS4937NTAG
NTMS4872NR2G	NTR4171PT1G	NTST30100CTH	NTTFS4937NTWG
NTMS4873NFR2G	NTR4501NT1G	NTST30100SG	NTTFS4939NTAG
NTMS4916NR2G	NTR4502PT1G	NTST30120CTG	NTTFS4939NTWG
NTMS4917NR2G	NTR4502PT3G	NTST30U100CTG	NTTFS4941NTAG
NTMS4920NR2G	NTR4503NT1G	NTST30U100CTH	NTTFS4941NTWG

Multisim 14.0 Power Pro Components

NTTFS4943NTAG	NTZD3154NT2G	NUF4401MNT1G	NUP4301MR6T1G
NTTFS4945NTAG	NTZD3154NT5G	NUF4403MNT1G	NUP4302MR6T1G
NTTFS4985NFTAG	NTZD3155CT1G	NUF6001MUT2G	NUP4304MR6T1G
NTTFS4985NFTWG	NTZD3155CT2G	NUF6105FCT1G	NUP45V6P5T5G
NTTFS4C05NTAG	NTZD3155CT5G	NUF6401MNT1G	NUS3116MTR2G
NTTFS4C05NTWG	NTZD5110NT1G	NUF6402MNT1G	NVB6413ANT4G
NTTFS4C06NTAG	NTZS3151PT1G	NUF8001MUT2G	NVD4804NT4G
NTTFS4C06NTWG	NUD3105DMT1G	NUF8401MNT4G	NVD5117PLT4G
NTTFS4C08NTAG	NUD3105LT1G	NUF8402MNT4G	NVD5802NT4G
NTTFS4C08NTWG	NUD3112DMT1G	NUF8410MNT4G	NVD5807NT4G
NTTFS4C10NTAG	NUD3112LT1G	NUF9002FCT1G	NVD5865NLT4G
NTTFS4C10NTWG	NUD3124DMT1G	NUMERIC_KEYPAD_ 4X4	NVD5890NT4G
NTTFS4C13NTAG	NUD3124LT1G	NUMERIC_KEYPAD_ 4X5	NVD6415ANLT4G
NTTFS4C13NTWG	NUD3160DMT1G		NVD6824NLT4G
NTTFS5811NLTAG	NUD3160LT1G	NUP1105LT1G	NVDD5894NLT4G
NTTFS5811NLTWG	NUF2042XV6T1G	NUP1301	NVF2955T1G
NTTFS5820NLTAG	NUF2114MNT1G	NUP1301ML3T1G	NVF3055-100T1G
NTTFS5820NLTWG	NUF2116MNT1G	NUP1301U	NVF3055L108T1G
NTUD3127CT5G	NUF2221W1T2G	NUP2105LT1G	NVF3055L108T3G
NTUD3128NT5G	NUF2230XV6T1G	NUP2202W1T2G	NVF5P03T3G
NTUD3169CZT5G	NUF2450MUT2G	NUP4102XV6T1G	NVF6P02T3G
NTUD3170NZT5G	NUF3101FCT1G	NUP4103FCT1G	NVMD3P03R2G
NTUD3171PZT5G	NUF3102MUTAG	NUP4201DR2G	NVMFD5485NLT1G
NTZD3152PT1G	NUF4001MUT2G	NUP4201MR6T1G	NVMFD5485NLT3G
NTZD3154NT1G	NUF4220MNT1G	NUP4202W1T2G	

Multisim 14.0 Power Pro Components

NVMFD5485NLWFT 1G	NVMFS5844NLT3G	NX3008NBKT	NZH18C
NVMFD5485NLWFT 3G	NVMFS5885NLT1G	NX3008NBKV	NZH20C
NVMFD5485NLWFT 3G	NVMFS5885NLT3G	NX3008NBKW	NZH22C
NVMFD5489NLT1G	NVMS4816NR2G	NX3008PBK	NZH24C
NVMFD5489NLT3G	NVR5198NLT1G	NX3008PBKMB	NZH27C
NVMFD5489NLWFT 1G	NVR5198NLT3G	NX3008PBKS	NZH30C
NVMFD5489NLWFT 3G	NVTA7002NT1G	NX3008PBKT	NZH3V0B
NVMFD5489NLWFT 3G	NVTFS4824NTAG	NX3008PBKV	NZH3V3A
NVMFD5852NLT1G	NVTFS4824NTWG	NX3008PBKW	NZH3V6B
NVMFD5852NLWFT 1G	NVTFS4C25NTAG	NX7002AK	NZH3V9B
NVMFD5852NLWFT 1G	NVTFS5116PLTAG	NX7002AKS	NZH4V3B
NVMFD5873NLT1G	NVTFS5116PLTWG	NX7002AKW	NZH4V7B
NVMFD5873NLWFT 1G	NVTFS5124PLTAG	NXP3875G	NZH5V1B
NVMFD5873NLWFT 1G	NVTFS5124PLTWG	NXP3875Y	NZH5V6B
NVMFD5877NLT1G	NVTFS5826NLTAG	NZ9F2V4ST5G	NZH6V2B
NVMFD5877NLT3G	NVTFS5826NLTWG	NZ9F2V4T5G	NZH6V8B
NVMFD5877NLWFT 1G	NVTJD4001NT1G	NZ9F2V7ST5G	NZH7V5C
NVMFD5877NLWFT 3G	NVTR01P02LT1G	NZ9F5V1T5G	NZH8V2B
NVMFD5877NLWFT 3G	NVTR0202PLT1G	NZ9F6V2ST5G	NZH9V1B
NVMFS5826NLT1G	NVTR4502PT1G	NZH10C	NZL5V6ATT1G
NVMFS5826NLT3G	NVTR4503NT1G	NZH11C	NZL5V6AXV3T1G
NVMFS5832NLT1G	NX2301P	NZH12B	NZL6V8AXV3T1G
NVMFS5834NLT1G	NX3008NBK	NZH13B	NZL7V5AXV3T1G
NVMFS5834NLT3G	NX3008NBKMB	NZH15B	NZQA5V6XV5T1G
NVMFS5844NLT1G	NX3008NBKS	NZH16C	NZQA6V8AXV5T1G

Multisim 14.0 Power Pro Components

NZQA6V8AXV5T2G	NZX22A	NZX5V6A	OP02AZ
NZQA6V8AXV5T3G	NZX22B	NZX5V6B	OP02CJ
NZX10A	NZX24A	NZX5V6C	OP02CP
NZX10C	NZX24B	NZX5V6D	OP02CZ
NZX11A	NZX27A	NZX5V6E	OP04AK
NZX11C	NZX27B	NZX6V2B	OP04AY
NZX11D	NZX27C	NZX6V2C	OP04EY
NZX12A	NZX2V4A	NZX6V2D	OP05AH
NZX12B	NZX2V7B	NZX6V2E	OP05AJ
NZX12C	NZX30A	NZX6V8A	OP05AJ8
NZX12D	NZX30C	NZX6V8B	OP05AZ
NZX13B	NZX33C	NZX6V8C	OP05CH
NZX13C	NZX36C	NZX7V5A	OP05CJ
NZX14A	NZX3V0B	NZX7V5B	OP05CJ8
NZX14B	NZX3V3B	NZX7V5D	OP05CN8
NZX14C	NZX3V3C	NZX8V2A	OP05CP
NZX15B	NZX3V6C	NZX8V2B	OP05CZ
NZX16A	NZX3V9C	NZX8V2D	OP05EH
NZX16B	NZX4V3C	NZX9V1B	OP05EJ
NZX16C	NZX4V7A	NZX9V1E	OP05EJ8
NZX18A	NZX4V7C	OCTAL_REG	OP05EN8
NZX18B	NZX4V7D	OL	OP05EP
NZX18C	NZX5V1B	OP01CZ	OP05EZ
NZX20A	NZX5V1C	OP01J	OP05H
NZX20B	NZX5V1D	OP02AJ	OP05J

Multisim 14.0 Power Pro Components

OP05J8	OP07J	OP15AJ	OP162GS
OP06AJ	OP07J8	OP15AZ	OP162GSZ
OP06GJ	OP07RC/883	OP15BH	OP16AH
OP06GZ	OP07Y	OP15BJ/883	OP16AJ
OP07AH	OP07Z	OP15BZ/883	OP16BH
OP07AJ	OP08	OP15CH	OP16BJ/883
OP07AJ8	OP09AY	OP15EH	OP16BZ/883
OP07AZ	OP09BY	OP15EJ	OP16C
OP07CD	OP10AY	OP15EZ	OP16CH
OP07CH	OP10CY	OP15FH	OP16EH
OP07CJ8	OP10EY	OP15FJ	OP16EJ
OP07CJG	OP10Y	OP15FP	OP16EZ
OP07CN8	OP113EP	OP15FZ	OP16FH
OP07CP	OP113ES	OP15GH	OP16FJ
OP07CS8	OP113FP	OP15GJ	OP16FP
OP07DD	OP113FS	OP15GN8	OP16FZ
OP07DJG	OP1177AR	OP15GP	OP16GH
OP07DP	OP1177ARM	OP15GS	OP16GJ
OP07ED	OP11GP	OP15GZ	OP16GN8
OP07EH	OP11GS	OP160ARC/883	OP16GP
OP07EJ8	OP12BJ	OP160AZ	OP16GS
OP07EJG	OP12BZ/883	OP160FZ	OP16GZ
OP07EN8	OP12EJ	OP160GP	OP176GP
OP07EP	OP12EZ	OP160GS	OP176GS
OP07H	OP15AH	OP162DRU	OP177AZ

Multisim 14.0 Power Pro Components

OP177BRC/883	OP207AY	OP215BRC/883	OP21AJ
OP177BZ	OP207EY	OP215BZ/883	OP21AZ
OP177EZ	OP207FY	OP215CH	OP21EZ
OP177FP	OP20BJ	OP215CJ/883	OP21FJ
OP177FS	OP20BZ	OP215CJ8	OP21FP
OP177FZ	OP20CZ	OP215CZ/883	OP21FZ
OP177GP	OP20FP	OP215EH	OP21GJ
OP177GS	OP20GJ	OP215EJ	OP21GP
OP177GZ	OP20GP	OP215EJ8	OP21HS
OP183GP	OP20GZ	OP215EN8	OP220AJ
OP183GS	OP20HJ	OP215EP	OP220AZ
OP184ES	OP20HS	OP215EZ	OP220CJ
OP191GP	OP20HZ	OP215FJ	OP220CZ
OP191GS	OP213AZ/883	OP215FP	OP220EZ
OP193EP	OP213BZ/883	OP215FZ	OP220FZ
OP193ES	OP213EP	OP215GH	OP220GJ
OP193FP	OP213ES	OP215GJ8	OP220GP
OP193FS	OP213EZ	OP215GN8	OP220GS
OP196GP	OP213FP	OP215GP	OP220GZ
OP196GS	OP213FS	OP215GS	OP221AJ/883
OP200AZ	OP215AH	OP215GZ	OP221AZ
OP200EZ	OP215AJ	OP2177AR	OP221BJ
OP200FZ	OP215AJ8	OP2177ARM	OP221CJ
OP200GP	OP215AZ	OP2177ARMZ	OP221EZ
OP200GS	OP215BJ/883	OP2177ARZ	OP221GJ

Multisim 14.0 Power Pro Components

OP221GP	OP249FZ	OP27AL	OP27GP
OP221GS	OP249GP	OP27AZ	OP27GPZ
OP221GZ	OP249GS	OP27BJ	OP27GS
OP227AJ	OP260AJ	OP27BR/883	OP27GSZ
OP227CJ	OP260ARC/883	OP27BZ	OP27GZ
OP227EJ	OP260GP	OP27CH	OP281GRU
OP227EN	OP260GS	OP27CJ	OP281GS
OP227GJ	OP262DRU	OP27CJ8	OP282AZ/883
OP227GN	OP262DRUZ-REEL	OP27CJG	OP282GP
OP22AJ/883	OP262GS	OP27CZ	OP282GS
OP22AZ	OP262GSZ	OP27EH	OP283GP
OP22HP	OP262HRUZ-REEL	OP27EJ	OP283GS
OP22HS	OP270EZ	OP27EJ8	OP284EP
OP22HZ	OP270FZ	OP27EN8	OP284ES
OP237AJ	OP270GP	OP27EP	OP284FP
OP237CJ	OP270GS	OP27EPZ	OP284FS
OP237EJ	OP275GP	OP27EZ	OP285GP
OP237EN	OP275GS	OP27FJ	OP285GS
OP237GJ	OP279GP	OP27FP	OP290ARC/883
OP237GN	OP279GS	OP27FZ	OP290AZ
OP249AJ	OP279HRU	OP27GH	OP290EZ
OP249ARC/883	OP27AH	OP27GJ	OP290FZ
OP249AZ	OP27AJ	OP27GJ8	OP290GP
OP249EJ	OP27AJ8	OP27GJZ	OP290GS
OP249FJ	OP27AJG	OP27GN8	OP291GP

Multisim 14.0 Power Pro Components

OP291GS	OP32FP	OP37FJ	OP4177ARUZ
OP292GP	OP32FZ	OP37FP	OP4177ARZ
OP292GS	OP32GP	OP37FZ	OP41AJ
OP293EP	OP32GZ	OP37GH	OP41BJ
OP293ES	OP37AFK	OP37GJ	OP41EJ
OP293FP	OP37AH	OP37GJ8	OP41FJ
OP293FS	OP37AJ	OP37GN8	OP41GP
OP295A	OP37AJ8	OP37GP	OP41GS
OP295AP	OP37AJG	OP37GS	OP420BY
OP295GP	OP37AL	OP37GZ	OP420CRC/883
OP295GS	OP37AZ	OP400ATC/883	OP420CY
OP296GP	OP37BJ	OP400AY	OP420FY
OP296GS	OP37BRC/883	OP400EY	OP420GP
OP296HRU	OP37BZ	OP400FY	OP420GS
OP297ARC/883	OP37CH	OP400GP	OP420GY
OP297AZ	OP37CJ	OP400GS	OP420HP
OP297AZ/883	OP37CJ8	OP400HP	OP420HS
OP297EZ	OP37CJG	OP400HS	OP420HY
OP297FP	OP37CZ	OP413EP	OP421BY
OP297FZ	OP37EH	OP413ES	OP421CY
OP297GP	OP37EJ	OP413EY	OP421FY
OP297GS	OP37EJ8	OP413FP	OP421GP
OP32AZ	OP37EN8	OP413FS	OP421GS
OP32EP	OP37EP	OP4177AR	OP421GY
OP32EZ	OP37EZ	OP4177ARU	OP421HP

Multisim 14.0 Power Pro Components

OP421HS	OP467ARC/883	OP490GS	OP497GY
OP421HY	OP467AY/883	OP491GP	OP50AY
OP42AJ	OP467GP	OP491GS	OP50BY
OP42ARC/883	OP467GS	OP491GSZ	OP50EY
OP42AZ	OP470ARC/883	OP492GP	OP50FY
OP42EJ	OP470ATC/883	OP492GS	OP61ARC/883
OP42EZ	OP470AY	OP493EP	OP61AZ
OP42FJ	OP470EY	OP493ES	OP61FZ
OP42FZ	OP470GP	OP493FP	OP61GP
OP42GP	OP470GS	OP493FS	OP61GS
OP42GS	OP481GRU	OP495GP	OP64AJ
OP43	OP481GS	OP495GS	OP64ARC/883
OP43A	OP482ARC/883	OP495GSZ	OP64AZ
OP43B	OP482AY/883	OP496GP	OP64GP
OP43E	OP482GP	OP496GS	OP64GS
OP43F	OP484EP	OP496HRU	OP727AR
OP43G	OP484ES	OP497AY	OP727ARU
OP44AJ	OP484FP	OP497BRC/883	OP727ARUZ
OP462DRU	OP484FPZ	OP497BY	OP747AR
OP462DRUZ-REEL	OP484FS	OP497CY	OP747ARU
OP462DS	OP490ATC/883	OP497FP	OP777AR
OP462GS	OP490AY	OP497FS	OP777ARM
OP462GSZ	OP490EY	OP497FY	OP77BJ
OP462HRU-REEL	OP490FY	OP497GP	OP77BRC/883
OP462HRUZ-REEL	OP490GP	OP497GS	OP77BZ

Multisim 14.0 Power Pro Components

OP77EZ	OP999	OPA131PA	OPA1642AID
OP77FJ	OPA1013CN8	OPA131PJ	OPA1642AIDGKR
OP77FZ	OPA1013DN8	OPA131UA	OPA1642AIDR
OP77GP	OPA111AM	OPA131UJ	OPA1644AID
OP77GS	OPA111BM	OPA132P	OPA1644AIPW
OP80BJ	OPA111SM	OPA132PA	OPA177EZ
OP80EJ	OPA121KM	OPA132U	OPA177FP
OP80FJ	OPA121KP	OPA132UA	OPA177FZ
OP80GP	OPA121KU	OPA134PA	OPA177GP
OP80GS	OPA124P	OPA134UA	OPA177GS
OP906	OPA124PA	OPA137N	OPA177GZ
OP90ARC/883	OPA124PB	OPA137NA	OPA209AID
OP90AZ	OPA124U	OPA137P	OPA209AIDBVR
OP90EZ	OPA124UA	OPA137PA	OPA209AIDGKR
OP90FZ	OPA124UB	OPA137U	OPA209AIDR
OP90GP	OPA128JM	OPA137UA	OPA2107AM
OP90GS	OPA128KM	OPA140AID	OPA2107AP
OP950	OPA128LM	OPA140AIDBVR	OPA2107AU
OP97AJ	OPA128SM	OPA140AIDGKR	OPA2107BM
OP97AZ	OPA129P	OPA140AIDR	OPA2107SM
OP97EP	OPA129PB	OPA141AIDGKR	OPA2111AM
OP97FJ	OPA129U	OPA141AIDR	OPA2111BM
OP97FP	OPA129UB	OPA1612AID	OPA2111KM
OP97FS	OPA130PA	OPA1632D	OPA2111KP
OP97FZ	OPA130UA	OPA1632DGN	OPA2111SM

Multisim 14.0 Power Pro Components

OPA211AID	OPA2137UA	OPA2251UA	OPA2333AIDRG4
OPA211AIDGKR	OPA2140AID	OPA2277P	OPA2334AIDGSR
OPA211AIDR	OPA2140AIDGKR	OPA2277PA	OPA2335AID
OPA211AIDRGR	OPA2140AIDR	OPA2277U	OPA2335AIDGKR
OPA211ID	OPA2141AIDGKR	OPA2277UA	OPA2335AIDR
OPA211IDGKR	OPA2141AIDR	OPA227P	OPA2337EA/250
OPA211IDR	OPA2209AID	OPA227PA	OPA2337PA
OPA211IDRGR	OPA2209AIDGKR	OPA227U	OPA2337UA
OPA2130PA	OPA2209AIDR	OPA227UA	OPA2338EA/250
OPA2130UA	OPA2227P	OPA228P	OPA2338UA
OPA2131PA	OPA2227PA	OPA228U	OPA2340EA
OPA2131PJ	OPA2227U	OPA2300AIDGSR	OPA2340PA
OPA2131UA	OPA2227UA	OPA2301AID	OPA2340UA
OPA2131UJ	OPA2234P	OPA2301AIDGKR	OPA2342EA
OPA2132P	OPA2234PA	OPA2301AIDR	OPA2342UA
OPA2132PA	OPA2234U	OPA2317ID	OPA2344EA/250
OPA2132U	OPA2234UA	OPA2317IDGKR	OPA2344PA
OPA2132UA	OPA2237EA	OPA2330AID	OPA2344UA
OPA2134PA	OPA2237UA	OPA2330AIDGKR	OPA2347EA
OPA2134UA	OPA2241PA	OPA2330AIDR	OPA2347UA
OPA2137E	OPA2241UA	OPA2330AIDRBR	OPA2349EA/250
OPA2137EA	OPA2244EA	OPA2330AIDRG4	OPA2349UA
OPA2137P	OPA2244PA	OPA2333AIDGKR	OPA234E
OPA2137PA	OPA2244UA	OPA2333AIDR	OPA234EA
OPA2137U	OPA2251PA	OPA2333AIDRBR	OPA234P

Multisim 14.0 Power Pro Components

OPA234PA	OPA2376AIYZDR	OPA2604AU	OPA2686U
OPA234U	OPA2377AID	OPA2613ID	OPA2690I-14D
OPA234UA	OPA2377AIDGKR	OPA2613IDTJ	OPA2690ID
OPA2350EA	OPA2377AIDR	OPA2614ID	OPA2691I-14D
OPA2350PA	OPA2378AIDCNR	OPA2614IDTJ	OPA2691ID
OPA2350UA	OPA2379AID	OPA2652E	OPA2703EA/250
OPA2353EA/250	OPA2379AIDCNR	OPA2652U	OPA2703PA
OPA2353UA	OPA2379AIDG4	OPA2658P	OPA2703UA
OPA2354AIDDA	OPA237NA	OPA2658PB	OPA2704EA/250
OPA2354AIDGKR	OPA237UA	OPA2658U	OPA2704PA
OPA2355DGSA/250	OPA2380AIDGKR	OPA2658UB	OPA2704UA
OPA2357AIDGSR	OPA2381AIDGKR	OPA2677T	OPA2725AID
OPA2363AIDGSR	OPA2381AIDRBT	OPA2677U	OPA2725AIDGKR
OPA2363AIRSVR	OPA241PA	OPA2680N	OPA2725AIDR
OPA2363IDGSR	OPA241UA	OPA2680U	OPA2726AIDGST
OPA2369AIDCNR	OPA244NA	OPA2681N	OPA2727AID
OPA2369AIDGKR	OPA244PA	OPA2681U	OPA2727AIDRBR
OPA2373AIDGSR	OPA244UA	OPA2682N	OPA2727AIDRG4
OPA2373AIDRCR	OPA251PA	OPA2682U	OPA2735AID
OPA2374AID	OPA251UA	OPA2683ID	OPA2735AIDGKR
OPA2374AIDCNR	OPA2541AM	OPA2683IDCNR	OPA2735AIDR
OPA2374AIDG4	OPA2541BM	OPA2683IDG4	OPA2743EA/250
OPA2376AID	OPA2541SM	OPA2683IDGST	OPA2743PA
OPA2376AIDGKR	OPA2544T	OPA2684ID	OPA2743UA
OPA2376AIDR	OPA2604AP	OPA2684IDCNR	OPA277P

Multisim 14.0 Power Pro Components

OPA277PA	OPA2836IRUNR	OPA337EA/250	OPA348AIDCKR
OPA277U	OPA2846ID	OPA337NA/250	OPA349NA
OPA277UA	OPA300AID	OPA337PA	OPA349SA
OPA27AJ	OPA300AIDBV	OPA337UA	OPA349UA
OPA27AZ	OPA301AID	OPA338NA/250	OPA350EA
OPA27BJ	OPA301AIDBV	OPA338UA	OPA350PA
OPA27BZ	OPA317ID	OPA340NA	OPA350UA
OPA27CJ	OPA317IDBVR	OPA340PA	OPA353NA
OPA27CZ	OPA317IDCKR	OPA340UA	OPA353UA
OPA27EJ	OPA320AIDBVR	OPA342NA	OPA354AIDBV
OPA27EZ	OPA320SAIDBVR	OPA342PA	OPA354AIDDA
OPA27FJ	OPA333AID	OPA342UA	OPA355NA
OPA27FZ	OPA333AIDBVR	OPA343NA	OPA355UA
OPA27GJ	OPA333AIDCKR	OPA343UA	OPA357AIDBV
OPA27GP	OPA333AIDG4	OPA344NA	OPA3583AM
OPA27GU	OPA334AID	OPA344PA	OPA3583JM
OPA27GZ	OPA335EA/250	OPA344UA	OPA358AIDCK
OPA2822E/250	OPA335UA	OPA345NA	OPA360AIDCK
OPA2822U	OPA335AID	OPA345UA	OPA363ID
OPA2835ID	OPA335AIDBV	OPA347NA	OPA363IDBV
OPA2835IDGS	OPA336N/250	OPA347PA	OPA364ID
OPA2835IRMCR	OPA336NA/250	OPA347SA	OPA364IDBV
OPA2835IRUNR	OPA336NJ/250	OPA347UA	OPA365AID
OPA2836ID	OPA336U	OPA348AID	OPA365AIDBVR
OPA2836IDGS	OPA336UA	OPA348AIDBV	OPA3680E

Multisim 14.0 Power Pro Components

OPA3680U	OPA379AID	OPA404SG	OPA4234U
OPA3681E	OPA379AIDBVR	OPA4130PA	OPA4234UA
OPA3681U	OPA379AIDCKR	OPA4130UA	OPA4237UA
OPA3682E	OPA379AIDG4	OPA4131NA	OPA4241PA
OPA3682U	OPA37AJ	OPA4131NJ	OPA4241UA
OPA3684ID	OPA37AZ	OPA4131PA	OPA4243EA
OPA3684IDBQT	OPA37BJ	OPA4131PJ	OPA4244EA
OPA3690ID	OPA37BZ	OPA4131UA	OPA4251PA
OPA3690IDBQR	OPA37CJ	OPA4132PA	OPA4251UA
OPA3690IDG4	OPA37CZ	OPA4132UA	OPA4277PA
OPA3691ID	OPA37EJ	OPA4134UA	OPA4277UA
OPA3691IDBQT	OPA37EZ	OPA4137P	OPA4317ID
OPA3692ID	OPA37FJ	OPA4137PA	OPA4317IPW
OPA3692IDBQT	OPA37FZ	OPA4137U	OPA4330AID
OPA369AIDCKR	OPA37GJ	OPA4137UA	OPA4330AIPW
OPA373AID	OPA37GP	OPA4140AID	OPA4330AIRGYR
OPA373AIDBV	OPA37GU	OPA4140AIPW	OPA4340EA
OPA374AID	OPA37GZ	OPA4141AID	OPA4340PA
OPA374AIDBV	OPA380AID	OPA4141AIPW	OPA4340UA
OPA377AID	OPA380AIDGK	OPA4209AIPW	OPA4342EA
OPA377AIDBVR	OPA381AIDGK	OPA4227PA	OPA4342PA
OPA377AIDCKR	OPA404AG	OPA4227UA	OPA4342UA
OPA377AIDR	OPA404BG	OPA4228PA	OPA4343EA
OPA378AIDBVR	OPA404KP	OPA4228UA	OPA4343NA
OPA378AIDCKR	OPA404KU	OPA4234PA	OPA4343UA

Multisim 14.0 Power Pro Components

OPA4347EA	OPA4658U	OPA541SM	OPA602AP
OPA4347UA	OPA4658UB	OPA544F	OPA602AU
OPA4348AID	OPA4684ID	OPA544T	OPA602BM
OPA4348AIP	OPA4684IPWT	OPA547T	OPA602BP
OPA4350EA	OPA4703EA/250	OPA548T	OPA602CM
OPA4350UA	OPA4703UA	OPA549S	OPA602SM
OPA4353EA	OPA4704EA/250	OPA549T	OPA603AP
OPA4353UA	OPA4704UA	OPA551FA/500	OPA603AU
OPA4354AID	OPA4743EA/250	OPA551FAKTWT	OPA604AP
OPA4354AIPWR	OPA4743UA	OPA551PA	OPA604AU
OPA4374AID	OPA4820ID	OPA551UA	OPA606KM
OPA4374AIPWR	OPA4820IPWR	OPA552FA/500	OPA606KP
OPA4377AIPW	OPA4872ID	OPA552FAKTWT	OPA606LM
OPA4379AIPWR	OPA501AM	OPA552PA	OPA620KG
OPA445AP	OPA501BM	OPA552UA	OPA620KP
OPA445BM	OPA501RM	OPA561PWP	OPA620KU
OPA445SM	OPA501SM	OPA564AIDWD	OPA620LG
OPA452TA	OPA502BM	OPA564AIDWP	OPA620SG
OPA453FAKTWT	OPA502SM	OPA567AIRHGR	OPA621KG
OPA454AIDDA	OPA511AM	OPA569AIDWP	OPA621KP
OPA4650P	OPA512BM	OPA600BM	OPA621KU
OPA4650PB	OPA512SM	OPA600CM	OPA621LG
OPA4650U	OPA541AM	OPA600SM	OPA621SG
OPA4658P	OPA541AP	OPA600TM	OPA622AP
OPA4658PB	OPA541BM	OPA602AM	OPA622AU

Multisim 14.0 Power Pro Components

OPA623AP	OPA641PB	OPA648U	OPA658U
OPA623AU	OPA641U	OPA650N	OPA659IDBVR
OPA627AM	OPA641UB	OPA650NB	OPA659IDRBR
OPA627AP	OPA642H	OPA650P	OPA671AP
OPA627AU	OPA642HSQ	OPA650PB	OPA675JG
OPA627BM	OPA642P	OPA650U	OPA675KG
OPA627BP	OPA642PB	OPA650UB	OPA675SG
OPA627SM	OPA642U	OPA651N	OPA676JG
OPA628AP	OPA642UB	OPA651NB	OPA676KG
OPA628AU	OPA643H	OPA651P	OPA676SG
OPA633KP	OPA643HSQ	OPA651PB	OPA678AG
OPA637AM	OPA643P	OPA651U	OPA678AP
OPA637AP	OPA643PB	OPA651UB	OPA678AU
OPA637AU	OPA643U	OPA653IDBVR	OPA678SG
OPA637BM	OPA643UB	OPA653IDRBR	OPA680N
OPA637BP	OPA644U	OPA654AM	OPA680P
OPA637SM	OPA644UB	OPA655H	OPA680U
OPA640H	OPA646H	OPA655HSQ	OPA681N
OPA640HSQ	OPA646HSQ	OPA655P	OPA681P
OPA640P	OPA646P	OPA655PB	OPA681U
OPA640U	OPA646PB	OPA655UB	OPA682N
OPA640UB	OPA646U	OPA656N	OPA682P
OPA641H	OPA646UB	OPA656U	OPA682U
OPA641HSQ	OPA648H	OPA658N	OPA683BV
OPA641P	OPA648P	OPA658P	OPA683ID

Multisim 14.0 Power Pro Components

OPA684ID	OPA704UA	OPA835IDBVR	OR3
OPA684IDBV	OPA725AID	OPA836IDBVR	OR3
OPA686N	OPA725AIDBV	OPA842ID	OR4
OPA686U	OPA726AID	OPA842IDBV	OR4
OPA687N	OPA726AIDGK	OPA843ID	OR5
OPA687U	OPA727AIDGKR	OPA843IDBVT	OR5
OPA690ID	OPA727AIDRBT	OPA846ID	OR6
OPA690IDBV	OPA728AIDGKT	OPA846IDBVT	OR6
OPA691ID	OPA728AIDRBT	OPA847ID	OR7
OPA691IDBV	OPA734AID	OPA847IDBV	OR7
OPA692ID	OPA734AIDBV	OPA860ID	OR8
OPA692IDBV	OPA735AID	OPAMP_3T_VIRTU AL	OR8
OPA693ID	OPA735AIDBV	OPAMP_5T_VIRTU AL	OSTV7163151
OPA693IDBVT	OPA743NA	OPAMP_RATED	OSTV7203101
OPA694ID	OPA743PA		OSTV7203151
OPA694IDBVR	OPA743UA	OPT101P	OVERLOAD
OPA695ID	OPA77EZ	OPT201KP	P121
OPA695IDBVT	OPA77FP	OPT202P	P123
OPA698ID	OPA77FZ	OPT209P	P4KE10CA-E3/54
OPA699ID	OPA77GP	OPT211P	P4KE300A/3
OPA703NA	OPA820ID	OPT301M	P4SMA36CA-E3/61
OPA703PA	OPA820IDBVR	OPTOCOUPLER_VIR TUAL	P6KE100A-E3/54
OPA703UA	OPA820IDG4		P6KE10A-E3/54
OPA704NA	OPA827AID	OR2	P6KE200A
OPA704PA	OPA827AIDGKR	OR2	P6KE200AG

Multisim 14.0 Power Pro Components

P6KE200ARLG	PA02	PA25A	PB_DPST
P6KE6.8A	PA02A	PA41	PB_DPST
P6KE6.8AG	PA03	PA41A	PB_NC
P6KE6.8ARLG	PA03A	PA41M/883	PB_NO
P6KE8.2A-E3/54	PA04	PA45	PB50
P6KE9.1A-E3/54	PA04A	PA51	PB58
P6SMB11CAT3G	PA05	PA51A	PB58A
P6SMB13AT3G	PA05A	PA51M/883	PBHV8115T
P6SMB15AT3G	PA07	PA81J	PBHV8115X
P6SMB18AT3G	PA07A	PA83	PBHV8115Z
P6SMB20AT3G	PA07M/883	PA83A	PBHV8118T
P6SMB22AT3G	PA08	PA83M/883	PBHV8140Z
P6SMB22CAT3G	PA08/883	PA84	PBHV8215Z
P6SMB24A-E3/52	PA08A	PA84A	PBHV8540T
P6SMB24AT3G	PA09	PA84M/883	PBHV8540X
P6SMB24CA-E3/52	PA09A	PA85	PBHV8540Z
P6SMB24CAT3G	PA10	PA85A	PBHV9040T
P6SMB33A-E3/52	PA10A	PA85M	PBHV9040X
P6SMB33AT3G	PA10M/883	PA87	PBHV9040Z
P6SMB36A-E3/52	PA12	PA87A	PBHV9050T
P6SMB43CAT3G	PA12A	PA88	PBHV9050Z
P6SMB6.8AT3G	PA12M/883	PA88A	PBHV9115T
P6SMB62AT3G	PA21	PA89	PBHV9115X
P6SMB68AT3G	PA21A	PA89A	PBHV9115Z
PA01	PA25	PAR_GEN_CHK	PBHV9215Z

Multisim 14.0 Power Pro Components

PBHV9540Z	PBLS4002Y	PBRP123ET	PBSS303NZ
PBLS1501V	PBLS4003D	PBRP123YT	PBSS303PD
PBLS1501Y	PBLS4003V	PBSS2515E	PBSS303PX
PBLS1502V	PBLS4003Y	PBSS2515M	PBSS303PZ
PBLS1502Y	PBLS4004D	PBSS2515MB	PBSS304ND
PBLS1503V	PBLS4004V	PBSS2515VPN	PBSS304NX
PBLS1503Y	PBLS4004Y	PBSS2515VS	PBSS304NZ
PBLS1504V	PBLS4005D	PBSS2515YPN	PBSS304PD
PBLS1504Y	PBLS4005V	PBSS2540E	PBSS304PX
PBLS2001D	PBLS4005Y	PBSS2540M	PBSS304PZ
PBLS2001S	PBLS6001D	PBSS2540MB	PBSS305ND
PBLS2002D	PBLS6002D	PBSS301ND	PBSS305NX
PBLS2002S	PBLS6003D	PBSS301NX	PBSS305NZ
PBLS2003D	PBLS6004D	PBSS301NZ	PBSS305PD
PBLS2003S	PBLS6005D	PBSS301PD	PBSS305PX
PBLS2004D	PBLS6021D	PBSS301PX	PBSS305PZ
PBLS2021D	PBLS6022D	PBSS301PZ	PBSS306NX
PBLS2022D	PBLS6023D	PBSS302ND	PBSS306NZ
PBLS2023D	PBLS6024D	PBSS302NX	PBSS306PX
PBLS2024D	PBRN113ET	PBSS302NZ	PBSS306PZ
PBLS4001D	PBRN113ZT	PBSS302PD	PBSS3515E
PBLS4001V	PBRN123ET	PBSS302PX	PBSS3515M
PBLS4001Y	PBRN123YT	PBSS302PZ	PBSS3515MB
PBLS4002D	PBRP113ET	PBSS303ND	PBSS3515VS
PBLS4002V	PBRP113ZT	PBSS303NX	PBSS3540E

Multisim 14.0 Power Pro Components

PBSS3540M	PBSS4041PT	PBSS4220V	PBSS4420D
PBSS3540MB	PBSS4041PX	PBSS4230PAN	PBSS4440D
PBSS4021NT	PBSS4041PZ	PBSS4230PANP	PBSS4480X
PBSS4021NX	PBSS4041SN	PBSS4230QA	PBSS4520X
PBSS4021NZ	PBSS4041SP	PBSS4230T	PBSS4540X
PBSS4021PT	PBSS4041SPN	PBSS4240DPN	PBSS4540Z
PBSS4021PX	PBSS4112PAN	PBSS4240T	PBSS4560PA
PBSS4021PZ	PBSS4112PANP	PBSS4240V	PBSS4580PA
PBSS4021SN	PBSS4120T	PBSS4240X	PBSS4612PA
PBSS4021SP	PBSS4130PAN	PBSS4240Y	PBSS4620PA
PBSS4021SPN	PBSS4130PANP	PBSS4250X	PBSS4630PA
PBSS4032ND	PBSS4130QA	PBSS4260PAN	PBSS5112PAP
PBSS4032NT	PBSS4130T	PBSS4260PANP	PBSS5120T
PBSS4032NX	PBSS4140DPN	PBSS4260QA	PBSS5130PAP
PBSS4032NZ	PBSS4140T	PBSS4320T	PBSS5130QA
PBSS4032PD	PBSS4140U	PBSS4320X	PBSS5130T
PBSS4032PT	PBSS4140V	PBSS4330PA	PBSS5140T
PBSS4032PX	PBSS4160DPN	PBSS4330X	PBSS5140U
PBSS4032PZ	PBSS4160DS	PBSS4350D	PBSS5140V
PBSS4032SN	PBSS4160PAN	PBSS4350SPN	PBSS5160DS
PBSS4032SP	PBSS4160PANP	PBSS4350SS	PBSS5160PAP
PBSS4032SPN	PBSS4160QA	PBSS4350T	PBSS5160QA
PBSS4041NT	PBSS4160T	PBSS4350X	PBSS5160T
PBSS4041NX	PBSS4160U	PBSS4350Z	PBSS5160U
PBSS4041NZ	PBSS4160V	PBSS4360Z	PBSS5160V

Multisim 14.0 Power Pro Components

PBSS5220T	PBSS5440D	PD70-01B/TR7	PDTA114TM
PBSS5220V	PBSS5480X	PD93-21C/TR8	PDTA114TMB
PBSS5230PAP	PBSS5520X	PD95-21B/TR10	PDTA114TT
PBSS5230QA	PBSS5540X	PDB-C134	PDTA114TU
PBSS5230T	PBSS5540Z	PDB-C134F	PDTA114YE
PBSS5240T	PBSS5560PA	PDB-C139	PDTA114YM
PBSS5240V	PBSS5580PA	PDB-C142D	PDTA114YMB
PBSS5240X	PBSS5612PA	PDB-C152SM	PDTA114YT
PBSS5240Y	PBSS5620PA	PDB-C156	PDTA114YU
PBSS5250T	PBSS5630PA	PDTA113EE	PDTA115EE
PBSS5250X	PBSS8110D	PDTA113EM	PDTA115EM
PBSS5260PAP	PBSS8110T	PDTA113EMB	PDTA115EMB
PBSS5260QA	PBSS8110X	PDTA113ET	PDTA115ET
PBSS5320D	PBSS8110Y	PDTA113EU	PDTA115EU
PBSS5320T	PBSS8110Z	PDTA113ZE	PDTA115TE
PBSS5320X	PBSS8510PA	PDTA113ZM	PDTA115TM
PBSS5330PA	PBSS9110D	PDTA113ZMB	PDTA115TMB
PBSS5330X	PBSS9110T	PDTA113ZT	PDTA115TT
PBSS5350D	PBSS9110X	PDTA113ZU	PDTA115TU
PBSS5350SS	PBSS9110Y	PDTA114EE	PDTA123EE
PBSS5350T	PBSS9110Z	PDTA114EM	PDTA123EM
PBSS5350X	PBSS9410PA	PDTA114EMB	PDTA123EMB
PBSS5350Z	PCP1208-TD-H	PDTA114ET	PDTA123ET
PBSS5360Z	PD15-22B/TR8	PDTA114EU	PDTA123EU
PBSS5420D	PD15-22C/TR8	PDTA114TE	PDTA123JE

Multisim 14.0 Power Pro Components

PDTA123JM	PDTA124XMB	PDTA144EMB	PDTC114EMB
PDTA123JMB	PDTA124XT	PDTA144ET	PDTC114ET
PDTA123JT	PDTA124XU	PDTA144EU	PDTC114EU
PDTA123JU	PDTA143EE	PDTA144TE	PDTC114TE
PDTA123TM	PDTA143EM	PDTA144TM	PDTC114TM
PDTA123TMB	PDTA143EMB	PDTA144TMB	PDTC114TMB
PDTA123TT	PDTA143ET	PDTA144TT	PDTC114TT
PDTA123TU	PDTA143EU	PDTA144TU	PDTC114TU
PDTA123YE	PDTA143TE	PDTA144VE	PDTC114YE
PDTA123YM	PDTA143TM	PDTA144VM	PDTC114YM
PDTA123YMB	PDTA143TMB	PDTA144VMB	PDTC114YMB
PDTA123YT	PDTA143TT	PDTA144VT	PDTC114YT
PDTA123YU	PDTA143TU	PDTA144VU	PDTC114YU
PDTA124EE	PDTA143XE	PDTA144WE	PDTC115EE
PDTA124EM	PDTA143XM	PDTA144WM	PDTC115EM
PDTA124EMB	PDTA143XMB	PDTA144WMB	PDTC115EMB
PDTA124ET	PDTA143XT	PDTA144WT	PDTC115ET
PDTA124EU	PDTA143XU	PDTA144WU	PDTC115EU
PDTA124TE	PDTA143ZE	PDTB113ET	PDTC115TE
PDTA124TM	PDTA143ZM	PDTB113ZT	PDTC115TM
PDTA124TMB	PDTA143ZMB	PDTB123ET	PDTC115TMB
PDTA124TT	PDTA143ZT	PDTB123TT	PDTC115TT
PDTA124TU	PDTA143ZU	PDTB123YT	PDTC115TU
PDTA124XE	PDTA144EE	PDTC114EE	PDTC123EE
PDTA124XM	PDTA144EM	PDTC114EM	PDTC123EM

Multisim 14.0 Power Pro Components

PDTC123EMB	PDTC124TMB	PDTC143ZMB	PDTD123ET
PDTC123ET	PDTC124TT	PDTC143ZT	PDTD123TT
PDTC123EU	PDTC124TU	PDTC143ZU	PDTD123YT
PDTC123JE	PDTC124XE	PDTC144EE	PDZ10B
PDTC123JM	PDTC124XM	PDTC144EM	PDZ11B
PDTC123JMB	PDTC124XMB	PDTC144EMB	PDZ12B
PDTC123JT	PDTC124XT	PDTC144ET	PDZ13B
PDTC123JU	PDTC124XU	PDTC144EU	PDZ15B
PDTC123TE	PDTC143EE	PDTC144TE	PDZ16B
PDTC123TM	PDTC143EM	PDTC144TM	PDZ18B
PDTC123TMB	PDTC143EMB	PDTC144TMB	PDZ2.7B
PDTC123TT	PDTC143ET	PDTC144TT	PDZ20B
PDTC123TU	PDTC143EU	PDTC144TU	PDZ22B
PDTC123YE	PDTC143TE	PDTC144VE	PDZ24B
PDTC123YM	PDTC143TM	PDTC144VM	PDZ3.0B
PDTC123YMB	PDTC143TMB	PDTC144VMB	PDZ3.3B
PDTC123YT	PDTC143TT	PDTC144VT	PDZ3.6B
PDTC123YU	PDTC143TU	PDTC144VU	PDZ3.9B
PDTC124EE	PDTC143XE	PDTC144WE	PDZ4.3B
PDTC124EM	PDTC143XM	PDTC144WM	PDZ4.7B
PDTC124EMB	PDTC143XMB	PDTC144WMB	PDZ5.1B
PDTC124ET	PDTC143XT	PDTC144WT	PDZ5.6B
PDTC124EU	PDTC143XU	PDTC144WU	PDZ6.2B
PDTC124TE	PDTC143ZE	PDTD113ET	PDZ6.8B
PDTC124TM	PDTC143ZM	PDTD113ZT	PDZ7.5B

Multisim 14.0 Power Pro Components

PDZ9.1B	PEMD18	PEMH30	PESD15VS1UL
PEMB1	PEMD19	PEMH4	PESD15VS1ULD
PEMB10	PEMD2	PEMH7	PESD15VS2UAT
PEMB11	PEMD20	PEMH9	PESD15VS2UQ
PEMB13	PEMD24	PEMT1	PESD15VS2UT
PEMB14	PEMD3	PEMX1	PESD15VS4UD
PEMB15	PEMD30	PEMZ1	PESD15VS5UD
PEMB16	PEMD4	PEMZ7	PESD15VU1UT
PEMB17	PEMD48	PESD12VL1BA	PESD16VX1UL
PEMB18	PEMD6	PESD12VL2BT	PESD1CAN
PEMB19	PEMD9	PESD12VS1UA	PESD1FLEX
PEMB2	PEMF21	PESD12VS1UB	PESD1LIN
PEMB20	PEMH1	PESD12VS1UJ	PESD24VL1BA
PEMB24	PEMH10	PESD12VS1UL	PESD24VL2BT
PEMB3	PEMH11	PESD12VS1ULD	PESD24VS1UA
PEMB30	PEMH13	PESD12VS2UAT	PESD24VS1UB
PEMB4	PEMH14	PESD12VS2UQ	PESD24VS1UL
PEMB9	PEMH15	PESD12VS2UT	PESD24VS1ULD
PEMD10	PEMH16	PESD12VS4UD	PESD24VS2UAT
PEMD12	PEMH17	PESD12VS5UD	PESD24VS2UQ
PEMD13	PEMH18	PESD12VU1UT	PESD24VS2UT
PEMD14	PEMH19	PESD12VV1BL	PESD24VS4UD
PEMD15	PEMH2	PESD15VL1BA	PESD24VS5UD
PEMD16	PEMH20	PESD15VL2BT	PESD24VU1UT
PEMD17	PEMH24	PESD15VS1UB	PESD2CAN

Multisim 14.0 Power Pro Components

PESD36VS1UL	PESD3V3V4UG	PESD5V0S1BB	PESD5V0V1BL
PESD36VS2UT	PESD3V3V4UK	PESD5V0S1BL	PESD5V0V1BLD
PESD3V3L1BA	PESD3V3V4UW	PESD5V0S1BLD	PESD5V0V4UF
PESD3V3L1UA	PESD5V0F1BL	PESD5V0S1UA	PESD5V0V4UG
PESD3V3L1UB	PESD5V0F1BLD	PESD5V0S1UB	PESD5V0V4UK
PESD3V3L1UL	PESD5V0F5UF	PESD5V0S1UJ	PESD5V0V4UW
PESD3V3L2BT	PESD5V0F5UV	PESD5V0S1UL	PESD5V0X1BCAL
PESD3V3L2UM	PESD5V0L1BA	PESD5V0S1ULD	PESD5V0X1BCL
PESD3V3L4UF	PESD5V0L1UA	PESD5V0S2BT	PESD5V0X1BL
PESD3V3L4UG	PESD5V0L1UB	PESD5V0S2UAT	PESD5V0X1BQ
PESD3V3L4UW	PESD5V0L1UL	PESD5V0S2UQ	PESD5V0X1BT
PESD3V3L5UF	PESD5V0L1ULD	PESD5V0S4UD	PESD5V0X1UAB
PESD3V3L5UK	PESD5V0L2BT	PESD5V0S4UF	PESD5V0X1UALD
PESD3V3L5UV	PESD5V0L2UM	PESD5V0S5UD	PESD5V0X1UB
PESD3V3L5UY	PESD5V0L4UF	PESD5V0U1BA	PESD5V0X1ULD
PESD3V3S1UB	PESD5V0L4UG	PESD5V0U1BB	PESD5V2S2UT
PESD3V3S1UL	PESD5V0L4UW	PESD5V0U1BL	PESD9V0V4UK
PESD3V3S2UAT	PESD5V0L5UK	PESD5V0U1BLD	PESD9X5.0L
PESD3V3S2UQ	PESD5V0L5UV	PESD5V0U1UA	PESD9X7.0L
PESD3V3S2UT	PESD5V0L5UY	PESD5V0U1UB	PG_13
PESD3V3S4UD	PESD5V0L6UAS	PESD5V0U1UL	PG_9_O_E
PESD3V3S4UF	PESD5V0L6US	PESD5V0U1UT	PGA206P
PESD3V3S5UD	PESD5V0L7BAS	PESD5V0U2BT	PGA206PA
PESD3V3U1UT	PESD5V0L7BS	PESD5V0V1BA	PGA206U
PESD3V3V4UF	PESD5V0S1BA	PESD5V0V1BB	PGA206UA

Multisim 14.0 Power Pro Components

PGA207P	PHPT61003PY	PIC16CR56A	PJ-102A
PGA207PA	PHT4NQ10LT	PIC16CR58B	PLD-JTAG-HDR
PGA207U	PHT6N06LT	PIC16CR83	PLL_VIRTUAL
PGA207UA	PHT6N06T	PIC16CR84	PLUS_MINUS_ONE
PHASE_ANGLE_CONTROLLER	PHT6NQ10T	PIC16F83	PLUS_MINUS_ONE_BLUE
PHASE_ANGLE_CONTROLLER_2PULSE	PHT8N06LT	PIC16F84	PLUS_MINUS_ONE_GREEN
PHASE_ANGLE_CONTROLLER_6PULSE	PI_CONTROLLER	PIC16F84A	PLUS_MINUS_ONE_ORANGE
PHILIPS-MIPS-HDR	PIC12C508	PIC18F6620-TQFP(64L)	PLUS_MINUS_ONE_YELLOW
PHN110	PIC12C508A	PIC18F6720-TQFP(64L)	PLVA2656A
PhonePlug	PIC12C509	PIC18F6720-TQFP(64L)	PLVA650A
PhonePlug2	PIC12C509A	PIC18F8620-TQFP(80L)	PLVA662A
PHOTO_DIODE_RATED	PIC12CE518	PIC18F8720-TQFP(80L)	PMBD353
PHOTO_TRANSISTOR_RATED	PIC12CE519	PID_CONTROLLER	PMBD354
PHOTODIODE	PIC12CR509A	PIECEWISE_LINEAR_CURRENT	PMBD6050
PHOTOTRANSISTOR	PIC16C505	PIECEWISE_LINEAR_VOLTAGE	PMBD6100
PHP125	PIC16C54	PIMC31	PMBD7000
PHP225	PIC16C54A	PIMN31	PMBD7100
PHPT60603NY	PIC16C54C	PIMT1	PMBD914
PHPT60603PY	PIC16C554	PIMZ2	PMBF170
PHPT61002NYC	PIC16C558	PJ-002B-SMT	PMBF4391
PHPT61002PYC	PIC16C56	PJ-007	PMBF4392
PHPT61003NY	PIC16C56A	PJ1-023	PMBF4393
	PIC16C58B		
	PIC16CR54A		
	PIC16CR54C		

Multisim 14.0 Power Pro Components

PMBF4416	PMBT2369	PMBTA42DS	PMBZ5245B
PMBF4416A	PMBT2907	PMBTA44	PMBZ5246B
PMBF5484	PMBT2907A	PMBTA45	PMBZ5247B
PMBF5485	PMBT3904	PMBTA56	PMBZ5248B
PMBF5486	PMBT3904M	PMBTA64	PMBZ5249B
PMBFJ108	PMBT3904MB	PMBTA92	PMBZ5250B
PMBFJ109	PMBT3904VS	PMBZ5226B	PMBZ5251B
PMBFJ110	PMBT3904YS	PMBZ5227B	PMBZ5252B
PMBFJ111	PMBT3906	PMBZ5228B	PMBZ5253B
PMBFJ112	PMBT3906M	PMBZ5229B	PMBZ5254B
PMBFJ113	PMBT3906MB	PMBZ5230B	PMBZ5255B
PMBFJ174	PMBT3906VS	PMBZ5231B	PMBZ5256B
PMBFJ175	PMBT3906YS	PMBZ5232B	PMBZ5257B
PMBFJ176	PMBT3946VPN	PMBZ5233B	PMDPB28UN
PMBFJ177	PMBT3946YPN	PMBZ5234B	PMDPB30XN
PMBFJ210	PMBT4401	PMBZ5235B	PMDPB38UNE
PMBFJ211	PMBT4403	PMBZ5236B	PMDPB42UN
PMBFJ212	PMBT5550	PMBZ5237B	PMDPB55XP
PMBFJ308	PMBT5551	PMBZ5238B	PMDPB56XN
PMBFJ309	PMBT6428	PMBZ5239B	PMDPB58UPE
PMBFJ310	PMBT6429	PMBZ5240B	PMDPB70EN
PMBS3904	PMBTA06	PMBZ5241B	PMDPB70XP
PMBS3906	PMBTA13	PMBZ5242B	PMDPB70XPE
PMBT2222	PMBTA14	PMBZ5243B	PMDPB85UPE
PMBT2222A	PMBTA42	PMBZ5244B	PMDPB95XNE

Multisim 14.0 Power Pro Components

PMDT290UNE	PMEG2010AEJ	PMEG3002AEB	PMEG3010EJ
PMDT670UPE	PMEG2010AET	PMEG3002AEL	PMEG3010EP
PMEG1020EA	PMEG2010BEA	PMEG3002AELD	PMEG3010ER
PMEG1020EH	PMEG2010BELD	PMEG3002AESF	PMEG3010ET
PMEG1020EJ	PMEG2010BER	PMEG3002EJ	PMEG3015EH
PMEG1020EV	PMEG2010BEV	PMEG3002TV	PMEG3015EJ
PMEG1030EH	PMEG2010EA	PMEG3005AEA	PMEG3015EV
PMEG1030EJ	PMEG2010EH	PMEG3005AESF	PMEG3020BEP
PMEG2005AEA	PMEG2010EJ	PMEG3005AEV	PMEG3020BER
PMEG2005AEL	PMEG2010EPA	PMEG3005CT	PMEG3020CEP
PMEG2005AELD	PMEG2010EPK	PMEG3005EB	PMEG3020CPA
PMEG2005AESF	PMEG2010ER	PMEG3005EH	PMEG3020DEP
PMEG2005AEV	PMEG2010ET	PMEG3005EJ	PMEG3020EH
PMEG2005BELD	PMEG2010EV	PMEG3005EL	PMEG3020EJ
PMEG2005CT	PMEG2015EA	PMEG3005ELD	PMEG3020EP
PMEG2005EB	PMEG2015EH	PMEG3005ESF	PMEG3020EPA
PMEG2005EH	PMEG2015EJ	PMEG3005ET	PMEG3020ER
PMEG2005EJ	PMEG2015EPK	PMEG3010BEA	PMEG3030BEP
PMEG2005EL	PMEG2015EV	PMEG3010BEP	PMEG3030EP
PMEG2005ELD	PMEG2020AEA	PMEG3010BER	PMEG3050BEP
PMEG2005EPK	PMEG2020CPA	PMEG3010BEV	PMEG3050EP
PMEG2005ESF	PMEG2020EH	PMEG3010CEH	PMEG4002AESF
PMEG2005ET	PMEG2020EJ	PMEG3010CEJ	PMEG4002EB
PMEG2010AEB	PMEG2020EPA	PMEG3010EB	PMEG4002EJ
PMEG2010AEH	PMEG2020EPK	PMEG3010EH	PMEG4002EL

Multisim 14.0 Power Pro Components

PMEG4002ELD	PMEG4020EPK	PMEG6020ER	PML260SN
PMEG4002ESF	PMEG4020ER	PMEG6020ETP	PML340SN
PMEG4005AEA	PMEG4020ETP	PMEG6020ETR	PMLL4148L
PMEG4005AEV	PMEG4020ETR	PMEG6030EP	PMLL4448
PMEG4005CT	PMEG4030EP	PMEG6030ETP	PMLL5225B
PMEG4005EH	PMEG4030ER	PMF170XP	PMLL5226B
PMEG4005EJ	PMEG4030ETP	PMF250XN	PMLL5227B
PMEG4005EPK	PMEG4050EP	PMF280UN	PMLL5228B
PMEG4005ET	PMEG4050ETP	PMF290XN	PMLL5229B
PMEG4010BEA	PMEG45A10EPD	PMF3800SN	PMLL5230B
PMEG4010BEV	PMEG45U10EPD	PMF400UN	PMLL5231B
PMEG4010CEH	PMEG6002EB	PMF63UN	PMLL5232B
PMEG4010CEJ	PMEG6002EJ	PMF77XN	PMLL5233B
PMEG4010CPA	PMEG6002TV	PMF780SN	PMLL5234B
PMEG4010EH	PMEG6010AED	PMF87EN	PMLL5235B
PMEG4010EJ	PMEG6010CEH	PMG45UN	PMLL5236B
PMEG4010EP	PMEG6010CEJ	PMG85XP	PMLL5237B
PMEG4010EPK	PMEG6010CPA	PMGD130UN	PMLL5238B
PMEG4010ER	PMEG6010ELR	PMGD175XN	PMLL5239B
PMEG4010ET	PMEG6010EP	PMGD280UN	PMLL5240B
PMEG4010ETP	PMEG6010ER	PMGD290XN	PMLL5241B
PMEG4010ETR	PMEG6010ETR	PMGD370XN	PMLL5242B
PMEG4015EPK	PMEG6020ELR	PMGD400UN	PMLL5243B
PMEG4020EP	PMEG6020EP	PMGD780SN	PMLL5244B
PMEG4020EPA	PMEG6020EPA	PMGD8000LN	PMLL5245B

Multisim 14.0 Power Pro Components

PMLL5246B	PMN25EN	PMP5501V	PMR400UN
PMLL5247B	PMN25UN	PMP5501Y	PMR670UPE
PMLL5248B	PMN27UP	PMPB10XNE	PMR780SN
PMLL5249B	PMN27XPE	PMPB11EN	PMSS3904
PMLL5250B	PMN28UN	PMPB12UN	PMSS3906
PMLL5251B	PMN34UN	PMPB13XNE	PMST2222
PMLL5252B	PMN34UP	PMPB15XN	PMST2222A
PMLL5253B	PMN35EN	PMPB15XP	PMST2369
PMLL5254B	PMN40LN	PMPB16XN	PMST2907A
PMLL5255B	PMN40UPE	PMPB19XP	PMST3904
PMLL5256B	PMN42XPE	PMPB20EN	PMST3906
PMLL5257B	PMN48XP	PMPB20UN	PMST4401
PMLL5258B	PMN50UPE	PMPB20XPE	PMST4403
PMLL5259B	PMN70XPE	PMPB23XNE	PMST5088
PMLL5260B	PMN80XP	PMPB27EP	PMST5089
PMLL5261B	PMP4201G	PMPB29XNE	PMST5550
PMLL5262B	PMP4201V	PMPB29XPE	PMST5551
PMLL5263B	PMP4201Y	PMPB33XN	PMST6428
PMLL5264B	PMP4501G	PMPB33XP	PMST6429
PMLL5265B	PMP4501V	PMPB43XPE	PMSTA05
PMLL5266B	PMP4501Y	PMPB47XP	PMSTA06
PMMT491A	PMP5201G	PMR280UN	PMSTA42
PMMT591A	PMP5201V	PMR290UNE	PMSTA55
PMN20EN	PMP5201Y	PMR290XN	PMSTA56
PMN22XN	PMP5501G	PMR370XN	PMSTA92

Multisim 14.0 Power Pro Components

PMT200EN	PMV65XP	PN3565	PN4354
PMT21EN	PMV90EN	PN3638	PN4355
PMT29EN	PMZ1000UN	PN3638A	PN4356
PMT760EN	PMZ250UN	PN3640	PN4391
PMV117EN	PMZ270XN	PN3641	PN4392
PMV160UP	PMZ350XN	PN3642	PN4393
PMV16UN	PMZ390UN	PN3643	PN4416
PMV170UN	PMZ760SN	PN3644	PN4416A
PMV185XN	PMZB290UN	PN3645	PN4916
PMV20XN	PMZB300XN	PN3646	PN4917
PMV213SN	PMZB350UPE	PN3694	PN5128
PMV22EN	PMZB370UNE	PN4118A	PN5129
PMV28UN	PMZB380XN	PN4119A	PN5133
PMV30UN	PMZB420UN	PN4121	PN5134
PMV30XN	PMZB670UPE	PN4122	PN5135
PMV31XN	PMZB790SN	PN4141	PN5136
PMV32UP	PN2222	PN4143	PN5137
PMV33UPE	PN2222A	PN4248	PN5138
PMV37EN	PN2369	PN4249	PN5139
PMV40UN	PN2369A	PN4250	PN5142
PMV45EN	PN2484	PN4250A	PN5179
PMV48XP	PN2906	PN4258	PN5910
PMV50UPE	PN2906A	PN4258A	PN930
PMV60EN	PN2907	PN4274	PNS40010ER
PMV65UN	PN2907A	PN4275	

Multisim 14.0 Power Pro Components

POLYNOMIAL_VOLT AGE	PS2501-4	PSMN017-80PS	PSMN1R1-40BS
POTENTIOMETER	PS2561-1	PSMN018-80YS	PSMN1R2-25YL
POTENTIOMETER_R ATED	PS2561-2	PSMN020-100YS	PSMN1R2-25YLC
POTENTIOMETER_V IRTUAL	PS2701-1	PSMN020-30MLC	PSMN1R2-30YLC
POWERVCO	PS2801-1	PSMN022-30PL	PSMN1R3-30YL
POWERVCO2	PS2801-4	PSMN025-100D	PSMN1R5-25YL
PROBE	PSMN011-60ML	PSMN026-80YS	PSMN1R5-30BLE
PROBE_BLUE	PSMN011-60MS	PSMN027-100PS	PSMN1R5-30YL
PROBE_DIG	PSMN011-80YS	PSMN027-100XS	PSMN1R5-30YLC
PROBE_DIG_BLUE	PSMN012-100YS	PSMN028-100YS	PSMN1R5-40ES
PROBE_DIG_GREEN	PSMN012-60YS	PSMN030-60YS	PSMN1R5-40PS
PROBE_DIG_ORAN GE	PSMN012-80PS	PSMN034-100PS	PSMN1R6-30PL
PROBE_DIG_RED	PSMN013-100BS	PSMN038-100YL	PSMN1R6-40YLC
PROBE_DIG_YELLOW	PSMN013-100ES	PSMN039-100YS	PSMN1R7-30YL
PRTR5V0U1T	PSMN013-100PS	PSMN040-100MSE	PSMN1R7-60BS
PRTR5V0U2X	PSMN013-100XS	PSMN041-80YL	PSMN1R8-30PL
PS2501-1	PSMN013-100YSE	PSMN045-80YS	PSMN1R8-40YLC
PS2501-2	PSMN013-30MLC	PSMN057-200B	PSMN1R9-40PL
	PSMN013-30YLC	PSMN059-150Y	PSMN2R0-30PL
	PSMN013-80YS	PSMN069-100YS	PSMN2R0-30YL
	PSMN014-40YS	PSMN075-100MSE	PSMN2R0-30YLE
	PSMN015-60PS	PSMN0R9-25YLC	PSMN2R0-60ES
	PSMN016-100PS	PSMN1R0-30YLC	PSMN2R0-60PS
	PSMN016-100XS	PSMN1R1-25YLC	PSMN2R1-40PL
	PSMN017-60YS	PSMN1R1-30PL	PSMN2R2-25YLC

Multisim 14.0 Power Pro Components

PSMN2R2-30YLC	PSMN3R5-80ES	PSMN5R0-100XS	PSMN7R8-120ES
PSMN2R2-40PS	PSMN3R5-80PS	PSMN5R0-30YL	PSMN7R8-120PS
PSMN2R5-30YL	PSMN3R8-100BS	PSMN5R0-80PS	PSMN8R0-40PS
PSMN2R5-60PL	PSMN3R9-25MLC	PSMN5R5-60YS	PSMN8R2-80YS
PSMN2R6-30YLC	PSMN3R9-60PS	PSMN5R6-100PS	PSMN8R3-40YS
PSMN2R6-40YS	PSMN3R9-60XS	PSMN5R6-100XS	PSMN8R5-100ES
PSMN2R6-60PS	PSMN4R0-25YLC	PSMN5R8-40YS	PSMN8R5-100PS
PSMN2R7-30PL	PSMN4R0-30YL	PSMN6R0-25YLB	PSMN8R5-100XS
PSMN2R8-25MLC	PSMN4R0-30YLD	PSMN6R0-30YL	PSMN8R5-60YS
PSMN2R8-40PS	PSMN4R0-40YS	PSMN6R0-30YLB	PSMN8R7-80PS
PSMN2R8-80BS	PSMN4R1-30YLC	PSMN6R0-30YLD	PSMN9R0-25MLC
PSMN2R9-25YLC	PSMN4R2-60PL	PSMN6R1-30YLD	PSMN9R5-100PS
PSMN2R9-30MLC	PSMN4R3-100ES	PSMN6R3-120ES	PSMN9R5-100XS
PSMN3R0-30MLC	PSMN4R3-100PS	PSMN6R3-120PS	PSMN9R5-30YLC
PSMN3R0-30YL	PSMN4R3-30PL	PSMN6R5-25YLC	PSMN9R8-30MLC
PSMN3R0-60ES	PSMN4R3-80ES	PSMN6R5-80PS	PSMNR90-30BL
PSMN3R0-60PS	PSMN4R3-80PS	PSMN7R0-100ES	PTVS10VP1UP
PSMN3R3-40YS	PSMN4R4-30MLC	PSMN7R0-100PS	PTVS10VP1UTP
PSMN3R3-60PL	PSMN4R4-80PS	PSMN7R0-100XS	PTVS10VS1UR
PSMN3R3-80BS	PSMN4R5-40PS	PSMN7R0-30MLC	PTVS10VS1UTR
PSMN3R3-80ES	PSMN4R6-100XS	PSMN7R0-30YL	PTVS11VP1UP
PSMN3R3-80PS	PSMN4R6-60PS	PSMN7R0-30YLC	PTVS11VP1UTP
PSMN3R4-30BLE	PSMN4R8-100BSE	PSMN7R0-60YS	PTVS11VS1UR
PSMN3R4-30PL	PSMN5R0-100ES	PSMN7R6-100BSE	PTVS11VS1UTR
PSMN3R5-30YL	PSMN5R0-100PS	PSMN7R6-60PS	PTVS12VP1UP

Multisim 14.0 Power Pro Components

PTVS12VP1UTP	PTVS18VS1UR	PTVS30VS1UTR	PTVS48VP1UP
PTVS12VS1UR	PTVS18VS1UTR	PTVS33VP1UP	PTVS48VP1UTP
PTVS12VS1UTR	PTVS20VP1UP	PTVS33VP1UTP	PTVS48VS1UR
PTVS13VP1UP	PTVS20VP1UTP	PTVS33VS1UR	PTVS48VS1UTR
PTVS13VP1UTP	PTVS20VS1UR	PTVS33VS1UTR	PTVS51VP1UP
PTVS13VS1UR	PTVS20VS1UTR	PTVS36VP1UP	PTVS51VP1UTP
PTVS13VS1UTR	PTVS22VP1UP	PTVS36VP1UTP	PTVS51VS1UR
PTVS14VP1UP	PTVS22VP1UTP	PTVS36VS1UR	PTVS51VS1UTR
PTVS14VP1UTP	PTVS22VS1UR	PTVS36VS1UTR	PTVS54VP1UP
PTVS14VS1UR	PTVS22VS1UTR	PTVS3V3P1UP	PTVS54VP1UTP
PTVS14VS1UTR	PTVS24VP1UP	PTVS3V3P1UTP	PTVS54VS1UR
PTVS15VP1UP	PTVS24VP1UTP	PTVS3V3S1UR	PTVS54VS1UTR
PTVS15VP1UTP	PTVS24VS1UR	PTVS3V3S1UTR	PTVS58VP1UP
PTVS15VS1UR	PTVS24VS1UTR	PTVS40VP1UP	PTVS58VP1UTP
PTVS15VS1UTR	PTVS26VP1UP	PTVS40VP1UTP	PTVS58VS1UR
PTVS16VP1UP	PTVS26VP1UTP	PTVS40VS1UR	PTVS58VS1UTR
PTVS16VP1UTP	PTVS26VS1UR	PTVS40VS1UTR	PTVS5V0P1UP
PTVS16VS1UR	PTVS26VS1UTR	PTVS43VP1UP	PTVS5V0P1UTP
PTVS16VS1UTR	PTVS28VP1UP	PTVS43VP1UTP	PTVS5V0S1UR
PTVS17VP1UP	PTVS28VP1UTP	PTVS43VS1UR	PTVS5V0S1UTR
PTVS17VP1UTP	PTVS28VS1UR	PTVS43VS1UTR	PTVS60VP1UP
PTVS17VS1UR	PTVS28VS1UTR	PTVS45VP1UP	PTVS60VP1UTP
PTVS17VS1UTR	PTVS30VP1UP	PTVS45VP1UTP	PTVS60VS1UR
PTVS18VP1UP	PTVS30VP1UTP	PTVS45VS1UR	PTVS60VS1UTR
PTVS18VP1UTP	PTVS30VS1UR	PTVS45VS1UTR	PTVS64VP1UP

Multisim 14.0 Power Pro Components

PTVS64VP1UTP	PTVS9V0P1UP	PUMD2	PUSH_VM
PTVS6V0P1UP	PTVS9V0P1UTP	PUMD20	PWM
PTVS6V0P1UTP	PTVS9V0S1UR	PUMD24	PWM_3PHASE
PTVS6V0S1UR	PTVS9V0S1UTR	PUMD3	PWM_COMPLEME NTARY
PTVS6V0S1UTR	PULLUP_RATED	PUMD30	PWM_SINUSOIDAL _3PHASE
PTVS6V5P1UP	PULSE_CURRENT	PUMD48	PWMCM
PTVS6V5P1UTP	PULSE_VOLTAGE	PUMD6	PWMCM2
PTVS6V5S1UR	PUMB1	PUMD9	PWMCMX
PTVS6V5S1UTR	PUMB11	PUMH1	PWMVM
PTVS7V0P1UP	PUMB13	PUMH10	PWMVM2
PTVS7V0P1UTP	PUMB14	PUMH11	PXT2222A
PTVS7V0S1UR	PUMB19	PUMH13	PXT2907A
PTVS7V0S1UTR	PUMB2	PUMH2	PXT4401
PTVS7V5P1UP	PUMB24	PUMH30	PXT4403
PTVS7V5P1UTP	PUMB3	PUMH4	PXTA14
PTVS7V5S1UR	PUMB30	PUMH7	PXTA42
PTVS7V5S1UTR	PUMB4	PUMH9	PXTA92
PTVS8V0P1UP	PUMB9	PUMT1	PZFI108
PTVS8V0P1UTP	PUMD10	PUMX1	PZFI109
PTVS8V0S1UR	PUMD12	PUMX2	PZFI110
PTVS8V0S1UTR	PUMD13	PUMZ1	PZT2222
PTVS8V5P1UP	PUMD14	PUMZ2	PZT2222A
PTVS8V5P1UTP	PUMD15	PUSH_BUTTON_DP ST	PZT2222AT1G
PTVS8V5S1UR	PUMD18	PUSH_CM	PZT2907
PTVS8V5S1UTR	PUMD19		

Multisim 14.0 Power Pro Components

PZT2907A	PZU10B2L	PZU12BA	PZU15B3A
PZT2907AT1	PZU10B3	PZU12BL	PZU15BA
PZT2907AT1G	PZU10B3A	PZU12DB2	PZU15BL
PZT2907AT3G	PZU10BA	PZU13B	PZU15DB2
PZT3904	PZU10BL	PZU13B1	PZU16B
PZT3906	PZU10DB2	PZU13B1A	PZU16B1
PZT43	PZU11B	PZU13B2	PZU16B1A
PZT4401	PZU11B1	PZU13B2A	PZU16B2
PZT4403	PZU11B1A	PZU13B2L	PZU16B2A
PZT651T1	PZU11B2	PZU13B3	PZU16B2L
PZT651T1G	PZU11B2A	PZU13B3A	PZU16B3
PZT751T1	PZU11B2L	PZU13BA	PZU16B3A
PZT751T1G	PZU11B3	PZU13BL	PZU16BA
PZTA14	PZU11B3A	PZU13DB2	PZU16BL
PZTA14T1	PZU11BA	PZU14B2	PZU16DB2
PZTA42	PZU11BL	PZU14B2A	PZU18B
PZTA44	PZU11DB2	PZU14B2L	PZU18B1
PZTA92	PZU12B	PZU14DB2	PZU18B1A
PZTA92T1G	PZU12B1	PZU15B	PZU18B2
PZTA93	PZU12B1A	PZU15B1	PZU18B2A
PZU10B	PZU12B2	PZU15B1A	PZU18B2L
PZU10B1	PZU12B2A	PZU15B2	PZU18B3
PZU10B1A	PZU12B2L	PZU15B2A	PZU18B3A
PZU10B2	PZU12B3	PZU15B2L	PZU18BA
PZU10B2A	PZU12B3A	PZU15B3	PZU18BL

Multisim 14.0 Power Pro Components

PZU18DB2	PZU22B1	PZU3.0B1	PZU3.6DB2
PZU2.4B	PZU22B1A	PZU3.0B1A	PZU3.9B
PZU2.4BA	PZU22B2	PZU3.0B2	PZU3.9B1
PZU2.4BL	PZU22B2A	PZU3.0B2A	PZU3.9B1A
PZU2.7B	PZU22B2L	PZU3.0B2L	PZU3.9B2
PZU2.7B1	PZU22B3	PZU3.0BA	PZU3.9B2A
PZU2.7B1A	PZU22B3A	PZU3.0BL	PZU3.9B2L
PZU2.7B2	PZU22BA	PZU3.0DB2	PZU3.9BA
PZU2.7B2A	PZU22BL	PZU3.3B	PZU3.9BL
PZU2.7B2L	PZU22DB2	PZU3.3B1	PZU3.9DB2
PZU2.7BA	PZU24B	PZU3.3B1A	PZU30B
PZU2.7BL	PZU24B1	PZU3.3B2	PZU30BA
PZU2.7DB2	PZU24B1A	PZU3.3B2A	PZU30BL
PZU20B	PZU24B2	PZU3.3B2L	PZU33B
PZU20B1	PZU24B2A	PZU3.3BA	PZU33BA
PZU20B1A	PZU24B2L	PZU3.3BL	PZU33BL
PZU20B2	PZU24B3	PZU3.3DB2	PZU36B
PZU20B2A	PZU24B3A	PZU3.6B	PZU36BA
PZU20B2L	PZU24BA	PZU3.6B1	PZU36BL
PZU20B3	PZU24BL	PZU3.6B1A	PZU4.3B
PZU20B3A	PZU24DB2	PZU3.6B2	PZU4.3B1
PZU20BA	PZU27B	PZU3.6B2A	PZU4.3B1A
PZU20BL	PZU27BA	PZU3.6B2L	PZU4.3B2
PZU20DB2	PZU27BL	PZU3.6BA	PZU4.3B2A
PZU22B	PZU3.0B	PZU3.6BL	PZU4.3B2L

Multisim 14.0 Power Pro Components

PZU4.3B3	PZU5.1BL	PZU6.8B1	PZU8.2B2A
PZU4.3B3A	PZU5.1DB2	PZU6.8B1A	PZU8.2B2L
PZU4.3BA	PZU5.6B	PZU6.8B2	PZU8.2B3
PZU4.3BL	PZU5.6B1	PZU6.8B2A	PZU8.2B3A
PZU4.3DB2	PZU5.6B1A	PZU6.8B2L	PZU8.2BA
PZU4.7B	PZU5.6B2	PZU6.8B3	PZU8.2BL
PZU4.7B1	PZU5.6B2A	PZU6.8B3A	PZU8.2DB2
PZU4.7B1A	PZU5.6B2L	PZU6.8BA	PZU9.1B
PZU4.7B2	PZU5.6B3	PZU6.8BL	PZU9.1B1
PZU4.7B2A	PZU5.6B3A	PZU6.8DB2	PZU9.1B1A
PZU4.7B2L	PZU5.6BA	PZU7.5B	PZU9.1B2
PZU4.7B3	PZU5.6BL	PZU7.5B1	PZU9.1B2A
PZU4.7B3A	PZU5.6DB2	PZU7.5B1A	PZU9.1B2L
PZU4.7BA	PZU6.2B	PZU7.5B2	PZU9.1B3
PZU4.7BL	PZU6.2B1	PZU7.5B2A	PZU9.1B3A
PZU4.7DB2	PZU6.2B1A	PZU7.5B2L	PZU9.1BA
PZU5.1B	PZU6.2B2	PZU7.5B3	PZU9.1BL
PZU5.1B1	PZU6.2B2A	PZU7.5B3A	PZU9.1DB2
PZU5.1B1A	PZU6.2B2L	PZU7.5BA	QL6250-4PQ208C
PZU5.1B2	PZU6.2B3	PZU7.5BL	QUAD_MUX_2TO1
PZU5.1B2A	PZU6.2B3A	PZU7.5DB2	QUAD_REG
PZU5.1B2L	PZU6.2BA	PZU8.2B	R145-32.768kHz
PZU5.1B3	PZU6.2BL	PZU8.2B1	R26-32.768kHz
PZU5.1B3A	PZU6.2DB2	PZU8.2B1A	R38-32.768kHz
PZU5.1BA	PZU6.8B	PZU8.2B2	R710XPT

Multisim 14.0 Power Pro Components

R711XPT	RC4559P	REF01CP	REF192GPZ
R712XPT	RCJ-011-SMT	REF01CPZ	REF192GRU
R714XPT	RCJ-32234	REF01CS	REF192GRUZ
RAD_PER_SEC_TO_ RPM	RD10	REF01EZ	REF192GS
RAD_TO_DEG	RD11	REF01HPZ	REF193GS
	RD12	REF01HS	REF193GSZ
RB520CS3002L	RD15	REF01HZ	REF194ES
RB520CS30L	RD15SB	REF02AJ	REF194GP
RB520S30	RD2.0S	REF02AJ/883C	REF194GSZ
RB521CS30L	RD2.2S	REF02AZ	REF195ES
RB521S30	RD2.4S	REF02CP	REF195FS
RB521S30T1G	RD2.7S	REF02CS	REF195GP
RB521S30T5G	RD3.0S	REF02CZ	REF195GPZ
RB751CS40	RD4.7	REF02EZ	REF195GRU
RB751S40	RD5.1	REF02HPZ	REF195GRUZ
RB751S40T1G	RD5.6	REF02HSZ	REF195GS
RB751V40	RD6.2	REF02HZ	REF196GRU
RC_CHAIN_CAUER	RD6.8	REF02RC	REF196GRU-REEL7
RC_CHAIN_FOSTER	RD7.5	REF02RC/883C	REF196GS
RC4136D	RD7.5SB	REF191ES	REF196GSZ
RC4136N	RD8.2	REF191GP	REF198ES
RC4558D	RD9.2	REF191GS	REF198FSZ
RC4558P	REF01AJ	REF192ES	REF198GP
RC4558Y	REF01AJ/883C	REF192FS	REF198GRU
RC4559D	REF01CJ	REF192GP	REF198GRUZ

Multisim 14.0 Power Pro Components

REF198GS	REF43FZ	REF5040IDGKR	RESOLVER
REF3012_SOT23_3	REF43GP	REF5040IDR	REVERSE_1A
REF3020_SOT23_3	REF43GPZ	REF5045AID	REVERSE_2A
REF3025_SOT23_3	REF43GS	REF5045AIDGKR	REVERSE_3A
REF3033_SOT23_3	REF5010AID	REF5045AIDR	REVERSE_4A
REF3040_SOT23_3	REF5010AIDGKR	REF5045ID	RFM12P08
REF3120AIDBZR	REF5010ID	REF5045IDGKR	RFP10P15
REF3212AIDBVR	REF5010IDGKR	REF5045IDR	RFP12P08
REF3220AIDBVR	REF5020AID	REF5050AID	RFP12P10
REF3225AIDBVR	REF5020AIDGKR	REF5050AIDGKR	RFP15P05
REF3230AIDBVR	REF5020ID	REF5050AIDR	RFP30P06
REF3233AIDBVR	REF5020IDGKR	REF5050ID	RFP5P12
REF3240AIDBVR	REF5025AID	REF5050IDGKR	RFP5P15
REF3312AIDBZR	REF5025AIDGKR	REF5050IDR	RFP6P08
REF3312AIDCKR	REF5025ID	REFVAR	RFP8P08
REF3318AIDBZR	REF5025IDGKR	REG_FILE_2Px4	RGF1A
REF3318AIDCKR	REF5030AID	REG_FILE_4x4	RGF1B
REF3320AIDBZR	REF5030AIDGKR	RELAY_NC	RGF1D
REF3320AIDCKR	REF5030ID	RELAY_NO	RGF1G
REF3325AIDBZR	REF5030IDGKR	RELAY_NONC	RGF1J
REF3325AIDCKR	REF5030IDR	RELAY1A_VIRTUAL	RGF1K
REF3330AIDBZR	REF5040AID	RELAY1B_VIRTUAL	RGF1M
REF3330AIDCKR	REF5040AIDGKR	RELAY1C_VIRTUAL	RGL34A
REF3333AIDBZR	REF5040AIDR	RESISTOR_RATED	RGL34B
REF3333AIDCKR	REF5040ID	RESISTOR_VIRTUAL	RGL34D

Multisim 14.0 Power Pro Components

RGL34G	RGP20D	RIBBON_14H	RIBBON_24V
RGL34J	RGP20G	RIBBON_14H_LATC H	RIBBON_24V_LATC H
RGP02-12E	RGP20J	RIBBON_14H_MNT	RIBBON_24V_MNT
RGP02-14E	RGP25A	RIBBON_14V	RIBBON_26H
RGP02-16E	RGP25B	RIBBON_14V_LATC H	RIBBON_26H_LATC H
RGP02-18E	RGP25D	RIBBON_14V_MNT	RIBBON_26H_MNT
RGP02-20E	RGP25G	RIBBON_16H	RIBBON_26V
RGP02-20E-E3/54	RGP25J	RIBBON_16H_LATC H	RIBBON_26V_LATC H
RGP10A	RGP25K	RIBBON_16H_MNT	RIBBON_26V_MNT
RGP10B	RGP25M	RIBBON_16V	RIBBON_30H
RGP10D	RGP30A	RIBBON_16V_LATC H	RIBBON_30H_LATC H
RGP10G	RGP30B	RIBBON_16V_MNT	RIBBON_30H_MNT
RGP10J	RGP30D	RIBBON_20H	RIBBON_30V
RGP10K	RGP30G	RIBBON_20H_LATC H	RIBBON_30V_LATC H
RGP10M	RGP30J	RIBBON_20H_MNT	RIBBON_30V_MNT
RGP10M-E3/54	RGP30K	RIBBON_20V	RIBBON_34H
RGP15A	RGP30M	RIBBON_20V_LATC H	RIBBON_34H_LATC H
RGP15B	R-HI-008068-2	RIBBON_20V_MNT	RIBBON_34H_MNT
RGP15D	RIBBON_10H	RIBBON_24H	RIBBON_34V
RGP15G	RIBBON_10H_LATC H	RIBBON_24H_LATC H	RIBBON_34V_LATC H
RGP15J	RIBBON_10H_MNT	RIBBON_24H_MNT	
RGP15K	RIBBON_10V		
RGP15M	RIBBON_10V_LATC H		
RGP20A	RIBBON_10V_MNT		
RGP20B			

Multisim 14.0 Power Pro Components

RIBBON_40H	RM4136W	RN1401	RN1510
RIBBON_40H_LATC H	RM4558JG	RN1402	RN1511
	RMB4S-E3/45	RN1403	RN1601
RIBBON_40H_MNT	RN1101	RN1404	RN1602
RIBBON_40V	RN1102	RN1405	RN1603
RIBBON_40V_LATC H	RN1103	RN1406	RN1604
RIBBON_40V_MNT	RN1104	RN1407	RN1605
RIBBON_50H	RN1105	RN1408	RN1606
RIBBON_50H_LATC H	RN1106	RN1409	RN1607
	RN1107	RN1421	RN1608
RIBBON_50H_MNT	RN1108	RN1422	RN1609
RIBBON_50V	RN1109	RN1423	RN1610
RIBBON_50V_LATC H	RN1110	RN1424	RN1611
	RN1111	RN1425	RN1701
RIBBON_50V_MNT	RN1301	RN1426	RN1702
RJH6674	RN1302	RN1427	RN1703
RJH6675	RN1303	RN1501	RN1704
RJH6676	RN1304	RN1502	RN1705
RJH6677	RN1305	RN1503	RN1706
RJH6678	RN1306	RN1504	RN1707
RJH6686	RN1307	RN1505	RN1708
RJH6687	RN1308	RN1506	RN1709
RJH6688	RN1309	RN1507	RN1710
RM4136FK	RN1310	RN1508	RN1711
RM4136J	RN1311	RN1509	RN2401

Multisim 14.0 Power Pro Components

RN2402	RN2509	S1G-E3/61T	SA6.0A-E3/54
RN2403	RN2510	S1J-E3/61T	SA6.0CA-E3/54
RN2404	RN2511	S1PG-E3/84A	SA7.0A
RN2405	RPM_TO_RAD_PER _SEC	S2800A	SA9.0CA-E3/54
RN2406	RS1G-E3/5AT	S2800B	SA90A
RN2407	RS1K-E3/61T	S2800D	SAB-C167CR-LM HA+
RN2408	RS2D-E3/52T	S2800M	SAB-C167CR-LM HA+
RN2409	RS2J-E3/52T	S2G-E3/52T	SAB-C167SR-LM HA+
RN2410	RS3D-E3/57T	S2SA1774G	SAB-C167SR-LM HA+
RN2411	RTD	S2SC4617G	SAB-C167SR-LM HA+
RN2421	RV4136D	S3D-E3/57T	SAB-C167SR-LM HA+
RN2422	RV4136N	S3M-E3/57T	SAC5.0-E3/54
RN2423	RV4558D	S4PD-M3/86A	SAF-C167CR-LM HA+
RN2424	RV4558P	S5227B	SAF-C167CR-LM HA+
RN2425	S1227-1010BQ	S5227G	SAF-C167CR-LM HA+
RN2426	S1227-1010BR	S5227J	SAF-XC164TM- 4F40F AA
RN2427	S1227-16BQ	S5227N	SAF-XC164TM- 4F40F AA
RN2501	S1227-16BR	SA11A	SAF-XC866-1FRA AB
RN2502	S1227-33BQ	SA15AG	SAF-XC866-1FRA AB
RN2503	S1227-33BR	SA15ARLG	SAF-XC866L-1FRA AB
RN2504	S1227-66BQ	SA26A	SAF-XC866L-1FRA AB
RN2505	S1227-66BR	SA2M-E3/5AT	SAF-XC866L-1FRA AB
RN2506	S1B-E3/61T	SA5.0A	SAF-XC866L-1FRA AB
RN2507	S1D-E3/61T	SA5.0A-E3/54	SAF-XC866L-1FRA AB
RN2508		SA5.0CA-E3/54	

Multisim 14.0 Power Pro Components

SAF-XC886-6FFA 5V AC	SAF-XC888LM-6FFA 5V AC	SAK-XC2285M-56F80L AA	SAK-XC2287-96F80L AC
SAF-XC886-6FFA 5V AC	SAK-C167CR-LM HA+	SAK-XC2285M-56F80L AA	SAK-XC2287M-104F80L AA
SAF-XC886CLM-6FFA 5V AC	SAK-C167CR-LM HA+	SAK-XC2285M-72F80L AA	SAK-XC2287M-104F80L AA
SAF-XC886CLM-6FFA 5V AC	SAK-C167SR-LM HA+	SAK-XC2285M-72F80L AA	SAK-XC2287M-56F80L AA
SAF-XC886CM-6FFA 5V AC	SAK-C167SR-LM HA+	SAK-XC2286-56F66L AC	SAK-XC2287M-56F80L AA
SAF-XC886CM-6FFA 5V AC	SAK-XC2264-56F66L AC	SAK-XC2286-56F66L AC	SAK-XC2287M-72F80L AA
SAF-XC886LM-6FFA 5V AC	SAK-XC2264-56F66L AC	SAK-XC2286-56F80L AC	SAK-XC2287M-72F80L AA
SAF-XC886LM-6FFA 5V AC	SAK-XC2264-56F80L AC	SAK-XC2286-56F80L AC	SAK-XC2766X-96F66L AC
SAF-XC888-6FFA 5V AC	SAK-XC2264-56F80L AC	SAK-XC2287-56F66L AC	SAK-XC2766X-96F66L AC
SAF-XC888-6FFA 5V AC	SAK-XC2267-56F66L AC	SAK-XC2287-56F66L AC	SAK-XC2786X-96F66L AC
SAF-XC888CLM-6FFA 5V AC	SAK-XC2267-56F66L AC	SAK-XC2287-56F80L AC	SAK-XC2786X-96F66L AC
SAF-XC888CLM-6FFA 5V AC	SAK-XC2267-56F80L AC	SAK-XC2287-56F80L AC	SAK-XC866-1FRA AB
SAF-XC888CM-6FFA 5V AC	SAK-XC2267-56F80L AC	SAK-XC2287-96F66L AC	SAK-XC866-1FRA AB
SAF-XC888CM-6FFA 5V AC	SAK-XC2285M-104F80L AA	SAK-XC2287-96F66L AC	SAK-XC866L-1FRA AB
SAF-XC888LM-6FFA 5V AC	SAK-XC2285M-104F80L AA	SAK-XC2287-96F80L AC	SAK-XC886-6FFA 5V AC

Multisim 14.0 Power Pro Components

SAK-XC886-6FFA 5V AC	SAMPLE_GENERIC	SB540	SBC846BLT1G
	SAMPLE_LOSSY	SB540-E3/54	SBC846BLT3G
SAK-XC886CLM-6FFA 5V AC	SAMPLE_MICROSTRIP	SB550	SBC846BPDW1T1G
SAK-XC886CLM-6FFA 5V AC	SAMPLE_OPENEND	SB560	SBC846BPDW1T2G
		SB560-E3/54	SBC847BDW1T1G
SAK-XC886CM-6FFA 5V AC	SAMPLE_RFCAP	SBAS16DXV6T1G	SBC847BDW1T3G
	SAMPLE_RFCOIL	SBAS20LT1G	SBC856ALT1G
SAK-XC886CM-6FFA 5V AC	SAMPLE_WAVEGUIDE	SBAT54CLT1G	SBC856BDW1T1G
SAK-XC886LM-6FFA 5V AC	SB	SBAV70LT1G	SBC856BDW1T3G
	SB01-15C-TB-E	SBAV70LT3G	SBC856BWT1G
SAK-XC886LM-6FFA 5V AC	SB040-E3/54	SBAV99LT1G	SBC857BDW1T1G
		SBAV99LT3G	SBCP56-10T1G
SAK-XC888-6FFA 5V AC	SB05-03Q-TL-E	SBAW56LT1G	SBCP56-16T1G
	SB1003M3-TL-E	SBAW56LT3G	SBCP56-16T3G
SAK-XC888-6FFA 5V AC	SB140A-E3/54	SBAW56TT1G	SBCP56T1G
SAK-XC888CLM-6FFA 5V AC	SB160-E3/54	SBC807-16LT1G	SBCP56T3G
	SB2H100-E3/54	SBC807-16LT3G	SBCP68T1G
SAK-XC888CLM-6FFA 5V AC	SB2H90-E3/23	SBC807-25LT1G	SBE001-TL-E
	SB320	SBC807-25LT3G	SBE002-TL-E
SAK-XC888CM-6FFA 5V AC	SB330	SBC807-40LT1G	SBR640CTT4G
SAK-XC888CM-6FFA 5V AC	SB340	SBC807-40LT3G	SBR660CTT4G
	SB350	SBC817-25LT1G	SBR80520LT1G
SAK-XC888LM-6FFA 5V AC	SB360	SBC817-25LT3G	SBR80520LT3G
	SB3H100-E3/54	SBC846ALT1G	SBR835LT4G
SAK-XC888LM-6FFA 5V AC	SB520	SBC846BDW1T1G	SBRA8160T3G
SAMPLE_BEND	SB530		

Multisim 14.0 Power Pro Components

SBRB1045G	SBR8140T3G	SEAM-40-07.0-S-06-2-A-K-TR	SEVEN_SEG_DECIMAL_COM_A_BLUE
SBRB1045T4G	SBR8190T3G		
SBRB1545CTG	SBR8320T3G	SEMICONDUCTOR_CAPACITOR_VIRTUAL	SEVEN_SEG_DECIMAL_COM_A_GREEN
SBRB1545CTT4G	SBR8340T3G	AL	SEVEN_SEG_DECIMAL_COM_A_ORANGE
SBRB20200CTT4G	SBS811-TL-E	SEMICONDUCTOR_RESISTOR_VIRTUAL	GE
SBRB2545CTG	SCH2202-TL-E	SEPICCM	SEVEN_SEG_DECIMAL_COM_A_YELLOW
SBRB2545CTT4G	SCHMITT_TRIGGER	SEPICVM	W
SBRD81035CTLT4G	SCR	SEVEN_SEG_COM_A	SEVEN_SEG_DECIMAL_COM_K
SBRD81045T4G	SCY99074DR2G		
SBRD8320G	SD05T1G	SEVEN_SEG_COM_A_BLUE	SEVEN_SEG_DECIMAL_COM_K_BLUE
SBRD8320T4G	SD12CT1G		
SBRD8330G	SD12T1G	SEVEN_SEG_COM_A_GREEN	SEVEN_SEG_DECIMAL_COM_K_GREEN
SBRD8330T4G	SD241		
SBRD8340G	SD41	SEVEN_SEG_COM_A_ORANGE	SEVEN_SEG_DECIMAL_COM_K_ORANGE
SBRD8340T4G	SDTA114YET1G	SEVEN_SEG_COM_A_YELLOW	E
SBRD8350G	SDTC114EET1G		SEVEN_SEG_DECIMAL_COM_K_YELLOW
SBRD8350T4G	SDTC114YET1G	SEVEN_SEG_COM_K	W
SBRD8360G	SDTC124EET1G	SEVEN_SEG_COM_K_BLUE	SEVEN_SEG_TWO-DIGIT_COM_A
SBRD8360RLG	SE10PJ-M3/84A		
SBRD8360T4G	SE5534AFK	SEVEN_SEG_COM_K_GREEN	SEVEN_SEG_TWO-DIGIT_COM_A_BLUE
SBRD8835LG	SE5534AJG		E
SBRD8835LT4G	SE5534FK	SEVEN_SEG_COM_K_ORANGE	SEVEN_SEG_TWO-DIGIT_COM_A_GREEN
SBR81100T3G	SE5534JG	SEVEN_SEG_COM_K_YELLOW	EN
SBR8120T3G	SEAM-40-03.0-S-06-2-A-K-TR		SEVEN_SEG_TWO-DIGIT_COM_A_ORANGE
SBR8130LT3G		SEVEN_SEG_DECIMAL_COM_A	NGE

Multisim 14.0 Power Pro Components

SEVEN_SEG_TWO-DIGIT_COM_A_YELLOW	SFH6136-X009T	SFH6701-X007	SFT1423-E
	SFH6136-X016	SFH6701-X009	SFT1423-TL-E
SEVEN_SEG_TWO-DIGIT_COM_K	SFH6136-X017T	SFH6702	SFT1440-E
	SFH6136-X018	SFH6702-X006	SFT1440-H
SEVEN_SEG_TWO-DIGIT_COM_K_BLUE	SFH6136-X019T	SFH6702-X007	SFT1440-TL-E
	SFH6156-3	SFH6702-X009T	SFT1440-TL-H
SEVEN_SEG_TWO-DIGIT_COM_K_GREEN	SFH6156-3T	SFH6705	SGL41-40-E3/96
	SFH615A-3	SFH6705-X006	SHIFT_4BIDI
SEVEN_SEG_TWO-DIGIT_COM_K_ORANGE	SFH615A-3X001	SFH6705-X007	SHIFT_4PIPO
	SFH615A-3X006	SFH6711	SHIFT_8PIN
SEVEN_SEG_TWO-DIGIT_COM_K_YELLOW	SFH615A-3X007T	SFH6711-X007	SHIFT_8POUT
	SFH615A-3X009T	SFH6712	Si1016CX-T1-GE3
	SFH615A-3X016	SFH6712-X007	Si1050X-T1-GE3
SFH 203 FA	SFH615A-3X017	SFH6719	Si1069X-T1-GE3
SFH 205 F	SFH617A-3	SFH6720T	Si1070X-T1-GE3
SFH 206 K	SFH617A-3X001	SFH6721T	Si1071X-T1-GE3
SFH 213	SFH617A-3X006	SFH6755T	Si1317DL-T1-GE3
SFH 229 FA	SFH617A-3X007T	SFH6756T	Si1403CDL-T1-GE3
SFH 2400 FA	SFH617A-3X016	SFH6757T	Si1416EDH-T1-GE3
SFH 2500 FA-Z	SFH617A-3X017T	SFH690CT	Si1469DH-T1-GE3
SFH 2505 FA-Z	SFH6316T	SFH690C-X001T	SI2302DS
SFH6136	SFH6343T	SFT1341-E	SI2304DS
SFH6136-X001	SFH6700	SFT1341-TL-E	Si2372DS-T1-GE3
SFH6136-X006	SFH6700-X009	SFT1345-H	Si2374DS-T1-GE3
SFH6136-X007	SFH6701	SFT1345-TL-H	Si5936DU-T1-GE3

Multisim 14.0 Power Pro Components

Si7121ADN-T1-GE3	Si9948DY	SiR640ADP-T1-GE3	SM15T10CA
Si7149ADP-T1-GE3	Si9950DY_N	SiR644DP-T1-GE3	SM15T12A
Si7456CDP-T1-GE3	Si9950DY_P	SiR880ADP-T1-GE3	SM15T12CA
Si8406DB-T2-E1	Si9953DY	SiS435DNT-T1-GE3	SM15T150A
Si8416DB-T2-E1	Si9956DY	SiS439DNT-T1-GE3	SM15T150A-E3/57T
Si8424CDB-T1-E1	SiA413ADJ-T1-GE3	SiS443DN-T1-GE3	SM15T150CA
Si8425DB-T1-E1	SiA437DJ-T1-GE3	SiS990DN-T1-GE3	SM15T150CA-E3/9AT
Si8461DB-T2-E1	SiA440DJ-T1-GE3	SiSA14DN-T1-GE3	SM15T15A
Si8469DB-T2-E1	SiA446DJ-T1-GE3	SJ1-3515N	SM15T15CA
Si8483DB-T2-E1	SiA462DJ-T1-GE3	SL05T1G	SM15T18A
Si8487DB-T1-E1	SiA906EDJ-T1-GE3	SL12-E3/5AT	SM15T18A-E3/57T
Si8497DB-T2-E1	SiA914ADJ-T1-GE3	SL13-E3/61T	SM15T18CA
Si8499DB-T2-E1	SiA922EDJ-T1-GE3	SL22-E3/52T	SM15T200A
Si8800EDB-T2-E1	SiA931DJ-T1-GE3	SL23-E3/52T	SM15T200CA
Si8802DB-T2-E1	SiA936EDJ-T1-GE3	SL43-E3/57T	SM15T220A
Si8851EDB-T2-E1	SiHB23N60E-GE3	SL44-E3/57T	SM15T220CA
Si9400DY	SiHB33N60E-GE3	SLOW_1A	SM15T22A
Si9405DY	SiHF23N60E-GE3	SLOW_2A	SM15T22CA
Si9410DY	SiHG33N60E-GE3	SLOW_3A	SM15T24A
Si9430DY	SiHG64N65E-GE3	SLOW_4A	SM15T24A-E3/9AT
Si9435DY	SiHG73N60E-GE3	SM05T1G	SM15T24CA
Si9933DY	SiHP33N60E-GE3	SM12T1G	SM15T27A
Si9942DY_P	SiJ470DP-T1-GE3	SM15T100A	SM15T27CA
Si9943DY_P	SiJ478DP-T1-GE3	SM15T100CA	SM15T30A
Si9947DY	SiR472ADP-T1-GE3	SM15T10A	

Multisim 14.0 Power Pro Components

SM15T30CA	SM4T10CA	SM4T220CA	SM4T39A
SM15T33A	SM4T12	SM4T22A	SM4T39C
SM15T33A-E3/57T	SM4T12A	SM4T22C	SM4T39CA
SM15T33CA	SM4T12C	SM4T22CA	SM4T68
SM15T36A	SM4T12CA	SM4T24	SM4T68A
SM15T36CA	SM4T15	SM4T24A	SM4T68C
SM15T39A	SM4T150	SM4T24C	SM4T68CA
SM15T39CA	SM4T150A	SM4T24CA	SM4T6V8
SM15T68A	SM4T150C	SM4T27	SM4T6V8A
SM15T68A-E3/57T	SM4T150CA	SM4T27A	SM4T6V8C
SM15T68CA	SM4T15A	SM4T27C	SM4T6V8CA
SM15T68CA-E3/57T	SM4T15C	SM4T27CA	SM4T7V5
SM15T6V8A	SM4T15CA	SM4T30	SM4T7V5A
SM15T6V8CA	SM4T18	SM4T30A	SM4T7V5C
SM15T7V5A	SM4T18A	SM4T30C	SM4T7V5CA
SM15T7V5CA	SM4T18C	SM4T30CA	SM5S20AHE3/2D
SM3G45	SM4T18CA	SM4T33	SM5S22AHE3/2D
SM3J45	SM4T200	SM4T33A	SM5S26AHE3/2D
SM4T10	SM4T200A	SM4T33C	SM5S33AHE3/2D
SM4T100	SM4T200C	SM4T33CA	SM5S36AHE3/2D
SM4T100A	SM4T200CA	SM4T36	SM6S33AHE3/2D
SM4T100C	SM4T22	SM4T36A	SM6T12A-E3/52
SM4T100CA	SM4T220	SM4T36C	SM8S12AHE3/2D
SM4T10A	SM4T220A	SM4T36CA	SM8S14AHE3/2D
SM4T10C	SM4T220C	SM4T39	SM8S15AHE3/2D

Multisim 14.0 Power Pro Components

SM8S16AHE3/2D	SMAJ6.5A-E3/61	SMBJ8.0A-E3/52	SMBTA55
SM8S17AHE3/2D	SMAJ60A-E3/61	SMBJ8.0CA-E3/52	SMBTA56
SM8S18AHE3/2D	SMBJ28CA-E3/52	SMBJ85A-E3/52	SMBTA56C
SM8S22AHE3/2D	SMBJ14A-E3/52	SMBT2222A	SMBTA70
SM8S24AHE3/2D	SMBJ15CA-E3/52	SMBT2907	SMBTA92
SM8S26AHE3/2D	SMBJ170A-E3/52	SMBT2907A	SMBTA93
SM8S30AHE3/2D	SMBJ188CA-E3/52	SMBT35200MT1G	SMCJ12A-E3/57T
SM8S33AHE3/2D	SMBJ22A-E3/52	SMBT3903	SMCJ130CA-E3/57T
SM8S36AHE3/2D	SMBJ24CA-E3/52	SMBT3904	SMCJ15A-E3/57T
SM8S43AHE3/2D	SMBJ26CA-E3/52	SMBT3906	SMCJ15CA-E3/57T
SMA5J28A-E3/61	SMBJ28CA-E3/52	SMBT3906S	SMCJ16CA-E3/57T
SMAJ11A-E3/61	SMBJ30A-E3/52	SMBT3946DW1T1G	SMCJ18A-E3/57T
SMAJ11CA-E3/61	SMBJ33A-E3/52	SMBT4124	SMCJ18CA-E3/57T
SMAJ12A-E3/61	SMBJ33CA-E3/52	SMBT4126	SMCJ26CA-E3/57T
SMAJ12CA-E3/61	SMBJ36A-E3/52	SMBT4401	SMCJ28CA-E3/57T
SMAJ150CA-E3/61	SMBJ36CA-E3/52	SMBT4403	SMCJ30CA-E3/57T
SMAJ15A-E3/61	SMBJ3V3-E3/52	SMBT5086	SMCJ33CA-E3/57T
SMAJ16A-E3/61	SMBJ45A-E3/52	SMBT5087	SMCJ36CA-E3/57T
SMAJ24A-E3/61	SMBJ48A-E3/52	SMBT6428	SMCJ48CA-E3/57T
SMAJ24CA-E3/61	SMBJ48CA-E3/52	SMBT6429	SMCJ5.0CA-E3/57T
SMAJ26A-E3/61	SMBJ5.0CA-E3/52	SMBTA05	SMCJ51CA-E3/57T
SMAJ28CA-E3/61	SMBJ58A-E3/52	SMBTA06	SMCJ58A-E3/57T
SMAJ36A-E3/61	SMBJ58CA-E3/52	SMBTA20	SMCJ6.5A-E3/57T
SMAJ40CA-E3/61	SMBJ6.0A-E3/52	SMBTA42	SMCJ75A-E3/57T
SMAJ530-E3/61	SMBJ70A-E3/52	SMBTA43	SMCJ78A-E3/57T

Multisim 14.0 Power Pro Components

SMCJ8.5A-E3/57T	SML4737	SML4762	SMMBTA42LT3G
SMF05CT1G	SML4738	SML4763	SMMBTA56LT1G
SMF05CT2G	SML4739	SMMBD2837LT1G	SMMBTA56LT3G
SMF12AT1G	SML4740	SMMBD301LT3G	SMMBTA92LT1G
SMF12CT1G	SML4741	SMMBD7000LT1G	SMMBTA92LT3G
SMF15CT1G	SML4742	SMMBD7000LT3G	SMMDL914T1G
SMF18AT1G	SML4743	SMMBD914LT1G	SMMJT350T1G
SMF22AT1G	SML4744	SMMBD914LT3G	SMMSD301T1G
SMF24AT1G	SML4745	SMMBT2222ALT1G	SMMSD4148T1G
SMF24CT1G	SML4746	SMMBT2222ALT3G	SMMSD4148T3G
SMF26AT1G	SML4747	SMMBT2369ALT1G	SMMUN2111LT1G
SMF28AT1G	SML4748	SMMBT2907ALT1G	SMMUN2111LT3G
SMF30AT1G	SML4749	SMMBT2907ALT3G	SMMUN2113LT1G
SMF33AT1G	SML4750	SMMBT3904LT1G	SMMUN2114LT1G
SMF36AT1G	SML4751	SMMBT3904TT1G	SMMUN2116LT1G
SMF48AT1G	SML4752	SMMBT4401LT1G	SMMUN2116LT3G
SMF5.0AT1G	SML4753	SMMBT4403LT1G	SMMUN2134LT1G
SMF58AT1G	SML4754	SMMBT5401LT1G	SMMUN2211LT1G
SMF6.0AT1G	SML4755	SMMBT5551LT1G	SMMUN2211LT3G
SMF6.5AT1G	SML4756	SMMBT5551LT3G	SMMUN2213LT1G
SMF7.0AT1G	SML4757	SMMBTA06LT1G	SMMUN2213LT3G
SMF7.5AT1G	SML4758	SMMBTA06LT3G	SMMUN2214LT1G
SMF8.0AT1G	SML4759	SMMBTA06WT1G	SMMUN2215LT1G
SML4735	SML4760	SMMBTA14LT1G	SMMUN2216LT1G
SML4736	SML4761	SMMBTA42LT1G	SMMUN2216LT3G

Multisim 14.0 Power Pro Components

SMMUN2233LT1G	SMUN5211T1G	SMUN5313DW1T1 G	SN74LS125AD
SMMUN2234LT1G	SMUN5211T3G		SN74LS125AN
SMS05T1G	SMUN5212T1G	SMUN5314DW1T1 G	SN74LS126AD
SMUN2111T1G	SMUN5213DW1T1 G	SMUN5315DW1T1 G	SN74LS126AN
SMUN2111T3G			SN74LS240DW
SMUN2114T1G	SMUN5213T1G	SMUN5330DW1T1 G	SN74LS240N
SMUN2211T1G	SMUN5214DW1T1 G	SMUN5335DW1T1 G	SN74LS244DW
SMUN2211T3G	SMUN5214T1G		SN74LS244N
SMUN2216T1G	SMUN5215T1G	SN10502D	SN74S244DW
SMUN2230T1G	SMUN5216DW1T1 G	SN10502DGK	SN74S244N
SMUN2232T1G		SN10502DGN	SN75173J
SMUN2240T1G	SMUN5230DW1T1 G	SN200501036DRE4	SN75173N
SMUN5112DW1T1 G	SMUN5232DW1T1 G	SN412008DRE4	SN75175D
SMUN5112T1G		SN54ABT25245JT	SN75175N
	SMUN5232T1G	SN7002N	SNSS30201MR6T1G
SMUN5113DW1T1 G	SMUN5233DW1T1 G	SN7002W	SNSS35200MR6T1G
SMUN5113T1G		SN74121N	SNSS40600CF8T1G
	SMUN5233T1G	SN74123D	SNUF6401MNT1G
SMUN5114DW1T1 G	SMUN5235DW1T1 G	SN74123FK	SONALERT
SMUN5114T1G		SN74123N	SPA02N80C3
	SMUN5237DW1T1 G	SN74130N	SPA03N60C3
SMUN5115DW1T1 G		SN74ABT244DB	SPA04N50C3
SMUN5115T1G	SMUN5311DW1T2 G	SN74ABT244DW	SPA04N60C3
		SN74ABT244N	SPA04N80C3
SMUN5116DW1T1 G	SMUN5312DW1T1 G		
		SN74ABT244PW	SPA06N60C3
SMUN5133T1G			

Multisim 14.0 Power Pro Components

SPA06N80C3	SPB08P06P G	SPD06N60C3	SPI07N60S5
SPA07N60C3	SPB100N03S2-03 G	SPD06N80C3	SPI08N50C3
SPA07N60CFD	SPB11N60C3	SPD07N60C3	SPI08N80C3
SPA08N50C3	SPB11N60S5	SPD07N60S5	SPI11N60C3
SPA08N80C3	SPB12N50C3	SPD08N50C3	SPI11N60CFD
SPA11N60C3	SPB16N50C3	SPD08P06P G	SPI11N60S5
SPA11N60CFD	SPB17N80C3	SPD09P06PL G	SPI12N50C3
SPA11N80C3	SPB18P06P G	SPD15P10P G	SPI15N60C3
SPA12N50C3	SPB20N60C3	SPD15P10PL G	SPI15N60CFD
SPA15N60C3	SPB20N60S5	SPD18P06P G	SPI16N50C3
SPA15N60CFD	SPB21N50C3	SPD30N03S2L-07 G	SPI20N60C3
SPA16N50C3	SPB80P06P G	SPD30N03S2L-10 G	SPI20N60CFD
SPA17N80C3	SPD01N60C3	SPD30N03S2L-20 G	SPI21N50C3
SPA20N60C3	SPD02N50C3	SPD30P06P G	SPP02N60C3
SPA20N60CFD	SPD02N60C3	SPD50N03S2-07 G	SPP02N60S5
SPA21N50C3	SPD02N60S5	SPD50N03S2L-06 G	SPP02N80C3
SPB02N60C3	SPD02N80C3	SPD50P03L G	SPP03N60C3
SPB02N60S5	SPD03N50C3	SPDT	SPP03N60S5
SPB03N60C3	SPD03N60C3	SPDT_CLOSED	SPP04N50C3
SPB03N60S5	SPD03N60S5	SPDT_DB	SPP04N60C3
SPB04N50C3	SPD04N50C3	SPDT_OPEN	SPP04N60S5
SPB04N60C3	SPD04N60C3	SPDT_SB	SPP04N80C3
SPB04N60S5	SPD04N60S5	SPEED_F	SPP06N60C3
SPB07N60C3	SPD04N80C3	SPEED_FR	SPP06N80C3
SPB07N60S5	SPD04P10PL G	SPI07N60C3	SPP07N60C3

Multisim 14.0 Power Pro Components

SPP07N60CFD	SPST_CLOSED	SPW20N60C3	SR_8PS_S_SL
SPP07N60S5	SPST_NC_DB	SPW20N60CFD	SR_8S_P
SPP08N50C3	SPST_NC_SB	SPW20N60S5	SR_FF
SPP08N80C3	SPST_NO_DB	SPW21N50C3	SR_FF_NEGSR
SPP08P06P H	SPST_NO_SB	SPW24N60C3	SR_FF_POSSR
SPP11N60C3	SPST_OPEN	SPW24N60CFD	SR_LATCH
SPP11N60CFD	SPU01N60C3	SPW32N50C3	SR_LATCH_NEGSR
SPP11N60S5	SPU02N60C3	SPW35N60C3	SS0503SH-TL-E
SPP11N80C3	SPU02N60S5	SPW35N60CFD	SS10P3-M3/86A
SPP12N50C3	SPU03N60C3	SPW47N60C3	SS10P4-M3/86A
SPP15N60C3	SPU03N60S5	SPW47N60CFD	SS10P6-M3/86A
SPP15N60CFD	SPU04N60C3	SPW52N50C3	SS10PH10-M3/86A
SPP15P10P H	SPU04N60S5	SPZT2222AT1G	SS14-E3/61T
SPP15P10PL H	SPU07N60C3	SPZT2907AT1G	SS16-E3/61T
SPP16N50C3	SPU07N60S5	SPZT651T1G	SS16T3G
SPP17N80C3	SPW07N60CFD	SQJ461EP-T1-GE3	SS1H10-E3/5AT
SPP18P06P H	SPW11N60C3	SQS482EN-T1-GE3	SS1P3L-M3/84A
SPP20N60C3	SPW11N60CFD	SR_4BIDI	SS1P4L-M3/84A
SPP20N60CFD	SPW11N60S5	SR_4P_P_3SO	SS1P4-M3/84A
SPP20N60S5	SPW11N80C3	SR_4P_P_INV	SS1P6L-E3/84A
SPP21N50C3	SPW12N50C3	SR_4S_P	SS22T3G
SPP24N60C3	SPW15N60C3	SR_8P_2S	SS24-E3/52T
SPP24N60CFD	SPW15N60CFD	SR_8P_S	SS24S-E3/61T
SPP80P06P H	SPW16N50C3	SR_8P_S_C	SS24T3
SPST	SPW17N80C3	SR_8PS_S_AS_L	SS24T3G

Multisim 14.0 Power Pro Components

SS26-E3/52T	SSC54-E3/57T	STD5407NT4G	SURA8160T3G
SS26T3	SSM2017P	STEP_CURRENT	SURA8210T3G
SS26T3G	SSM2017S	STEP_VOLTAGE	SURA8215T3G
SS2H10-E3/2CT	SSM2135S	STEPPER_FULLSTEP _2PHASE	SURA8220T3G
SS2P3L-M3/84A	SSM2212RZ	STEPPER_HALFSTEP _2PHASE	SURA8240T3G
SS2P4-M3/84A	SSM2212RZ-R7	STEPPER_MOTOR_ 2PHASE	SURB1620CTT4G
SS2PH10-M3/84A	SSM2212RZ-RL	STEPPER_MOTOR_ 2PHASE	SURD8320T4G
SS32	SSRD8620CTRG	STEPPER_MOTOR_ 2PHASE_2WINDING	SURD8330T4G
SS32-E3/57T	SSRD8620CTT4G	STEPPER_WAVE_2P HASE	SURD8530T4G
SS33	SSRD8620CTT4RG		SURHB8840CTT4G
SS34	SST174		SURHD8560T4G
SS34-E3/57T	SST175	STF202-22T1G	SURHD8560W1T4G
SS35	SST176	STP32N06L	SURHS8160T3G
SS36-E3/57T	ST10F168- PQFP(144)	SUD17N25-165-E3	SURS340DT3G
SS3P4HM3/84A	ST10F269T3- TQFP(144)	SUR620CTT4G	SURS360DBT3G
SS3P4LHM3/86A	ST10R272L- TQFP(100)	SUR81520G	SURS360DT3G
SS3P6-E3/84A	ST5771-1	SUR81560G	SURS8105T3G
SS5P10-M3/86A	ST7263B-SDIP(32)	SUR83020PTG	SURS8110T3G
SS5P6-M3/86A	ST7263B-SO(34)	SUR83060PTG	SURS8115T3G
SS8P3L-M3/86A	STD110N02RT4G	SUR8820G	SURS8120T3G
SS8PH10-M3/86A	STD24N06LT4G	SUR8840G	SURS8140T3G
SSA24-E3/61T	STD2955T4G	SURA8110T3G	SURS8160T3G
SSA33L-E3/61T	STD5406NT4G	SURA8120T3G	SURS8205T3G
SSA34-E3/61T		SURA8130T3G	SURS8210T3G
SSC53L-E3/57T		SURA8140T3G	SURS8220T3G

Multisim 14.0 Power Pro Components

SURS8320T3G	SZ1.5SMC62AT3G	SZ1SMB5921BT3G	SZBZX84C5V6LT1G
SURS8340T3G	SZ1SMA30AT3G	SZ1SMB5922BT3G	SZBZX84C5V6LT3G
SURS8360BT3G	SZ1SMA40CAT3G	SZ1SMB5924BT3G	SZBZX84C68LT1G
SURS8360T3G	SZ1SMA5913BT3G	SZ1SMB5925BT3G	SZBZX84C6V2LT1G
SWHYSTE	SZ1SMA5918BT3G	SZ1SMB5927BT3G	SZBZX84C6V2LT3G
SXT2222A	SZ1SMA5921BT3G	SZ1SMB5931BT3G	SZBZX84C6V8LT1G
SXT2907A	SZ1SMA5922BT3G	SZ1SMB5933BT3G	SZBZX84C6V8LT3G
SXT3904	SZ1SMA5927BT3G	SZ1SMB5934BT3G	SZBZX84C75LT1G
SXT3906	SZ1SMA5932BT3G	SZ1SMB5935BT3G	SZBZX84C9V1LT1G
SXTA42	SZ1SMA5936BT3G	SZ1SMB5936BT3G	SZBZX84C9V1LT3G
SXTA43	SZ1SMA5940BT3G	SZ1SMB5937BT3G	SZESD5Z5.0T1G
SXTA92	SZ1SMB14AT3G	SZ1SMB5939BT3G	SZESD5Z7.0T1G
SXTA93	SZ1SMB24AT3G	SZ1SMC36AT3G	SZESD9B5.0ST5G
SYNCHRONOUS_M ACHINE_PERMANE NT_MAGNET	SZ1SMB24CAT3G	SZBZX84B16LT1G	SZMM3Z10VT1G
	SZ1SMB26CAT3G	SZBZX84C12LT1G	SZMM3Z12VST1G
SYNCHRONOUS_M ACHINE_PERMANE NT_MAGNET_E	SZ1SMB28AT3G	SZBZX84C15LT1G	SZMM3Z15VT1G
	SZ1SMB28CAT3G	SZBZX84C15LT3G	SZMM3Z18VT1G
	SZ1SMB30AT3G	SZBZX84C33LT1G	SZMM3Z20VT1G
SYNCHRONOUS_M ACHINE_PERMANE NT_MAGNET_HALL	SZ1SMB30CAT3G	SZBZX84C33LT3G	SZMM3Z2V4T1G
	SZ1SMB33CAT3G	SZBZX84C36LT1G	SZMM3Z3V3ST1G
SZ1.5SMC15AT3G			
	SZ1SMB5.0AT3G	SZBZX84C3V0LT1G	SZMM3Z3V6T1G
SZ1.5SMC20AT3G			
	SZ1SMB58CAT3G	SZBZX84C4V7LT1G	SZMM3Z43VT1G
SZ1.5SMC33AT3G			
	SZ1SMB5918BT3G	SZBZX84C4V7LT3G	SZMM3Z4V3ST1G
SZ1.5SMC39AT3G			
	SZ1SMB5919BT3G	SZBZX84C5V1LT1G	SZMM3Z4V7T1G
SZ1.5SMC43AT3G			
	SZ1SMB5920BT3G	SZBZX84C5V1LT3G	SZMM3Z5V1T1G

Multisim 14.0 Power Pro Components

SZMM3Z5V6ST1G	SZMMBZ27VALT1G	SZMMSZ12T1G	SZMMSZ5242BT1G
SZMM5Z10VT1G	SZMMBZ27VALT3G	SZMMSZ2V7T1G	SZMMSZ5242BT3G
SZMM5Z12VT1G	SZMMBZ27VCLT1G	SZMMSZ3V3T1G	SZMMSZ5243BT1G
SZMM5Z16VT1G	SZMMBZ33VALT1G	SZMMSZ4678T1G	SZMMSZ5245BT1G
SZMM5Z18VT1G	SZMMBZ5221BLT1 G	SZMMSZ4683T1G	SZMMSZ5246BT1G
SZMM5Z20VT1G	SZMMBZ5222BLT1 G	SZMMSZ4688T1G	SZMMSZ5254BT1G
SZMM5Z24VT1G	SZMMBZ5231BLT1 G	SZMMSZ4689T1G	SZMMSZ5258BT1G
SZMM5Z27VT1G	SZMMBZ5231BLT1 G	SZMMSZ4690T1G	SZMMSZ5258BT3G
SZMM5Z36VT1G	SZMMBZ5231BLT3 G	SZMMSZ4690T3G	SZMMSZ5259BT1G
SZMM5Z3V0T1G	SZMMBZ5232BLT1 G	SZMMSZ4691T1G	SZMMSZ5260BT1G
SZMM5Z3V3T1G	SZMMBZ5232BLT1 G	SZMMSZ4692T1G	SZMMSZ5262BT1G
SZMM5Z4V7ST1G	SZMMBZ5240BLT1 G	SZMMSZ4696T1G	SZMSQA6V1W5T2G
SZMM5Z4V7ST5G	SZMMBZ5242BLT1 G	SZMMSZ4699T1G	SZNUP1105LT1G
SZMM5Z5V1T1G	SZMMBZ5248BLT1 G	SZMMSZ4705T1G	SZNUP1301ML3T1G
SZMM5Z5V6ST1G	SZMMBZ5254BLT1 G	SZMMSZ4715T1G	SZNUP2105LT1G
SZMM5Z5V6T1G	SZMMBZ5256BLT1 G	SZMMSZ5221BT1G	SZNUP4301MR6T1 G
SZMM5Z6V2ST1G	SZMMBZ5254BLT1 G	SZMMSZ5225BT1G	SZNUP4304MR6T1 G
SZMM5Z6V8ST1G	SZMMBZ5256BLT1 G	SZMMSZ5228BT1G	SZNZ9F2V7ST5G
SZMM5Z6V8T1G	SZMMBZ5256BLT1 G	SZMMSZ5231BT1G	SZNZ9F6V2ST5G
SZMM5Z7V5T1G	SZMMBZ5V6ALT1G	SZMMSZ5234BT1G	SZP6SMB15AT3G
SZMM5Z8V2ST1G	SZMMQA15VT1G	SZMMSZ5235BT1G	SZP6SMB18AT3G
SZMMBZ15VDLT1G	SZMMQA5V6T1G	SZMMSZ5236BT1G	SZP6SMB20AT3G
SZMMBZ15VDLT3G	SZMMQA6V2T1G	SZMMSZ5239BT1G	SZP6SMB33AT3G
SZMMBZ20VALT1G	SZMMSZ10T1G	SZMMSZ5240BT1G	SZP6SMB43CAT3G

Multisim 14.0 Power Pro Components

SZP6SMB51AT3G	TA75339F	TC1411EOA	TC4404CPA
SZP6SMB6.8AT3G	TA75339FB	TC1411EPA	TC4404EOA
SZP6SMB62AT3G	TA75339P	TC1411EUA	TC4404EPA
SZSMF12CT1G	TA75393F	TC1411NCOA	TC4405COA
SZSMF33AT1G	TA75393FB	TC1411NCPA	TC4405CPA
T_FF	TA75393P	TC1411NEOA	TC4405EOA
T_FF_NEGSR	TA75393PA	TC1411NEPA	TC4405EPA
T50RIA10	TA75393S	TC1411NEUA	TC4420CAT
T50RIA120	TA7805F	TC1411NVOA	TC4420COA
T50RIA20	TA7809F	TC1411NVPA	TC4420CPA
T50RIA40	TA7812F	TC1411NVUA	TC4420EMF
T50RIA60	TA7815F	TC1411VOA	TC4420EOA
T50RIA80	TC1410COA	TC1411VPA	TC4420EPA
T70RIA10	TC1410CPA	TC1411VUA	TC4420IJA
T70RIA120	TC1410EOA	TC1412COA	TC4420MJA
T70RIA20	TC1410EPA	TC1412CPA	TC4420VAT
T70RIA40	TC1410EUA	TC1412EOA	TC4420VMF
T70RIA60	TC1410NCOA	TC1412EPA	TC4420VOA
T70RIA80	TC1410NCPA	TC1412EUA	TC4420VPA
T90RIA10	TC1410NEOA	TC1412NCOA	TC4421AVMF
T90RIA120	TC1410NEPA	TC1412NCPA	TC4421CAT
T90RIA20	TC1410NEUA	TC1412NEOA	TC4421CPA
T90RIA40	TC1410NVUA	TC1412NEPA	TC4421EMF713
T90RIA60	TC1411COA	TC1412NEUA	TC4421EPA
T90RIA80	TC1411CPA	TC4404COA	TC4421ESM

Multisim 14.0 Power Pro Components

TC4421MJA	TC4424AVMF	TC4426AEOA713	TC4428COA
TC4421VAT	TC4424AVOA	TC4426COA	TC4428CPA
TC4421VMF	TC4424AVOE	TC4426CPA	TC4428EMF
TC4421VPA	TC4424AVPA	TC4426EMF	TC4428EOA
TC4422CAT	TC4424COE	TC4426EOA	TC4428EPA
TC4422CPA	TC4424CPA	TC4426EPA	TC4428EUA
TC4422EAT	TC4424EMF	TC4426EUA	TC4428VMF
TC4422EPA	TC4424EOE	TC4426MJA	TC4428VOA
TC4422ESM	TC4424EPA	TC4426VMF	TC4428VUA
TC4422MJA	TC4424MJA	TC4426VUA	TC4429COA713
TC4422VAT	TC4424VMF	TC4427ACOA713	TC4429EMF
TC4422VMF	TC4424VOE	TC4427AEOA713	TC4429EOA713
TC4422VPA	TC4424VPA	TC4427COA	TC4429IJA
TC4423AVMF	TC4425AVMF	TC4427CPA	TC4429MJA
TC4423AVOA	TC4425AVOA	TC4427EMF	TC4429VAT
TC4423AVOE	TC4425AVOE	TC4427EOA	TC4429VMF
TC4423AVPA	TC4425AVPA	TC4427EPA	TC4429VOA
TC4423COE	TC4425COE	TC4427EUA713	TC4429VPA
TC4423CPA	TC4425CPA	TC4427VMF	TC4431COA
TC4423EOE	TC4425EOE	TC4427VOA	TC4431CPA
TC4423EPA	TC4425EPA	TC4427VUA	TC4431EOA
TC4423MJA	TC4425VMF	TC4428ACOA713	TC4431EPA
TC4423VMF	TC4425VOE	TC4428AEJA	TC4431VOA
TC4423VOE	TC4425VPA	TC4428AEOA713	TC4431VPA
TC4423VPA	TC4426ACOA713	TC4428AMJA	TC4432COA

Multisim 14.0 Power Pro Components

TC4432CPA	TCET1100G	TDZ16J	TEMD5010X01
TC4432EOA	TCET1600	TDZ18J	TEMD5020X01
TC4432EPA	TCET1600G	TDZ20J	TEMD5110X01
TC4432VOA	TCLT1003	TDZ22J	TEMD5510FX01
TC4432VPA	TCMT1103	TDZ24J	TEMD6010FX01
TC4451VAT	TCMT1600	TDZ27J	TEMP_NC
TC4451VMF	TCMT4600	TDZ2V4J	TEMP_NO
TC4451VOA	TD_SW1	TDZ2V7J	TEMPERATURE_SO URCE
TC4451VPA	TDA2030	TDZ30J	TEMPLATE_1P1S_T MODEL
TC4452VAT	TDE1890_SO20	TDZ3V0J	TEMPLATE_1P2S_C OUPLED
TC4452VMF	TDE1890_ZIP11	TDZ3V3J	TEMPLATE_1P2S_N ON_LINEAR
TC4452VOA	TDE1891_SIP11	TDZ3V6J	TEMPLATE_1P2S_T AP_TMODEL
TC4452VPA	TDE1891_ZIP11	TDZ3V9J	TEMPLATE_1P2S_T MODEL
TC4467COE	TDE1897C_DIP8	TDZ4V3J	TEST_LABEL
TC4467CPD	TDE1897C_SO20	TDZ4V7J	TEST_PT_SMT
TC4467EOE713	TDE1898C_DIP8	TDZ5V1J	TEST_PT_THT
TC4468COE	TDE1898C_SIP9	TDZ5V6J	TGF148_1000B
TC4468CPD	TDE1898C_SO20	TDZ6V2J	TGF148_1100B
TC4468EOE713	TDM_CURRENT	TDZ6V8J	TGF148_600B
TC4468MOE	TDM_VOLTAGE	TDZ7V5J	TGF148_700B
TC4469COE	TDZ10J	TDZ8V2J	TGF148_800B
TC4469CPD	TDZ11J	TDZ9V1J	TEMD1000
TC4469EJD	TDZ12J	TEMD1000	TEMD1020
TC4469MJD	TDZ13J	TEMD1020	TEMD1030
TCET1100	TDZ15J	TEMD1030	

Multisim 14.0 Power Pro Components

TGF148_900B	THS3111CDGNR	THS4001ID	THS4032IDGN
THERMAL_NOISE	THS3111DGN	THS4011CD	THS4041CD
THERMAL_OL	THS3111ID	THS4011CDGN	THS4041CDGN
THERMAL_OL_RELAY	THS3111IDGN	THS4011ID	THS4041ID
THREE_PHASE_DELTA	THS3120CDGN	THS4011MFKB	THS4041IDGN
THREE_PHASE_WYE	THS3120DGN	THS4012CD	THS4042CD
THS3001CD	THS3120ID	THS4012CDGN	THS4042CDGN
THS3001CDGN	THS3120IDGN	THS4012ID	THS4042ID
THS3001ID	THS3121CD	THS4021CD	THS4042IDGN
THS3001IDGN	THS3121ID	THS4021CDGN	THS4051CD
THS3061D	THS3121IDGN	THS4021ID	THS4051CDGN
THS3061DGN	THS3122CD	THS4021IDGN	THS4051ID
THS3062D	THS3122CDDA	THS4022CD	THS4051IDGN
THS3062DDA	THS3122ID	THS4022CDGN	THS4051MFK
THS3062DGN	THS3122IDDA	THS4022ID	THS4051MJG
THS3091D	THS3125CPWP	THS4022IDGN	THS4052CD
THS3091DDA	THS3125ID	THS4031CD	THS4052CDGN
THS3095D	THS3125IPWP	THS4031CDGN	THS4052ID
THS3095DDA	THS3201D	THS4031ID	THS4052IDGN
THS3110DGN	THS3201DBVT	THS4031IDGN	THS4061CD
THS3110ID	THS3201DGK	THS4031MFK	THS4061CDGN
THS3110IDGN	THS3202D	THS4031MJG	THS4061ID
THS3110IDR	THS3202DGK	THS4032CD	THS4061IDGN
THS3111CD	THS3202DGN	THS4032CDGN	THS4061MFK
	THS4001CD	THS4032ID	THS4061MJG

Multisim 14.0 Power Pro Components

THS4062CD	THS4140CDGK	THS4221DGN	THS4500IDGK
THS4062CDGN	THS4140ID	THS4222D	THS4500IDGN
THS4062ID	THS4140IDGK	THS4222DGK	THS4501CD
THS4062IDGN	THS4141CD	THS4222DGN	THS4501CDGK
THS4081CD	THS4141CDGK	THS4225D	THS4501CDGN
THS4081CDGN	THS4141ID	THS4225DGK	THS4501ID
THS4081ID	THS4141IDGK	THS4225DGN	THS4501IDGK
THS4081IDGN	THS4150CD	THS4226DGQ	THS4501IDGN
THS4082CD	THS4150CDGK	THS4271D	THS4502CD
THS4082CDGN	THS4150ID	THS4271DGK	THS4502CDGK
THS4082ID	THS4150IDGK	THS4271DGN	THS4502ID
THS4082IDGN	THS4151CD	THS4271DR	THS4502IDGK
THS4120CD	THS4151CDGK	THS4271DRBT	THS4503CD
THS4120CDGK	THS4151ID	THS4281D	THS4503CDGK
THS4121CD	THS4151IDGK	THS4281DBVR	THS4503CDGN
THS4121CDGK	THS4211D	THS4281DGK	THS4503ID
THS4130CD	THS4211DGK	THS4302RGTT	THS4503IDGK
THS4130CDGK	THS4211DGN	THS4303RGTT	THS4503IDGN
THS4130ID	THS4215D	THS4304D	THS4505D
THS4130IDGK	THS4215DGK	THS4304DBVT	THS4505DGK
THS4131CD	THS4215DGN	THS4304DGK	THS4508RGTR
THS4131CDGK	THS4215DRBT	THS4500CD	THS4509RGT
THS4131ID	THS4221D	THS4500CDGK	THS4511RGTT
THS4131IDGK	THS4221DBV	THS4500CDGN	THS4513RGTR
THS4140CD	THS4221DGK	THS4500ID	THS4520RGTR

Multisim 14.0 Power Pro Components

THS4601CD	THS6043ID	THS6182DWP	TIMED_NOTO
THS4601CDDA	THS6043IPWP	THS6182RHFR	TI-MSP430-HDR
THS4601CDG4	THS6052CD	THS6184PWP	TIP100G
THS4601ID	THS6052CDDA	THS6184RHFR	TIP101G
THS4601IDDA	THS6052ID	THS7001CPWP	TIP102G
THS4601IDG4	THS6052IDDA	THS7001IPWP	TIP105
THS4631D	THS6053CPWPR	THS7002CPWP	TIP106G
THS4631DDA	THS6053ID	THS7002IPWP	TIP107G
THS4631DGN	THS6053IPWP	THS7530PWP	TIP110G
THS6002CDWP	THS6062CD	TIL191	TIP111G
THS6002IDWP	THS6062CDGN	TIL192	TIP112G
THS6007IPWP	THS6062ID	TIL193	TIP115G
THS6012CDWP	THS6062IDGN	TIME_DELAY_1A	TIP116G
THS6012IDWP	THS6072CD	TIME_DELAY_1C	TIP117G
THS6012IGQER	THS6072CDGN	TIME_DELAY_2A	TIP120G
THS6022CPWP	THS6072ID	TIME_DELAY_2C	TIP121G
THS6022IPWP	THS6072IDGNR	TIME_DELAY_3A	TIP122G
THS6032CDWP	THS6092CDDA	TIME_DELAY_3C	TIP125G
THS6032IDWP	THS6092ID	TIME_DELAY_4A	TIP126G
THS6032IVFPG4	THS6092IDDA	TIME_DELAY_4C	TIP127G
THS6042CDDA	THS6093CPWP	TIME_DELAY_NC	TIP140G
THS6042ID	THS6093ID	TIME_DELAY_NO	TIP141G
THS6042IDDA	THS6093IPWP	TIMED_NCTC	TIP142G
THS6043CD	THS6182D	TIMED_NCTO	TIP147G
THS6043CPWP	THS6182DW	TIMED_NOTC	TIP2955G

Multisim 14.0 Power Pro Components

TIP29AG	TIP41A	TL022CD	TL032AMJG
TIP29BG	TIP41AG	TL022CP	TL032AMJL
TIP29CG	TIP41B	TL022MJG	TL032AMP
TIP3055G	TIP41BG	TL022MU	TL032CD
TIP30CG	TIP41C	TL031ACD	TL032CP
TIP31A	TIP41CG	TL031ACP	TL032ID
TIP31AG	TIP42A	TL031AID	TL032IP
TIP31B	TIP42AG	TL031AIP	TL032MD
TIP31BG	TIP42B	TL031AMD	TL032MFK
TIP31C	TIP42BG	TL031AMFK	TL032MJG
TIP31CG	TIP42C	TL031AMJG	TL032ML
TIP31G	TIP42CG	TL031AML	TL032MP
TIP32A	TIP42G	TL031AMP	TL034ACD
TIP32AG	TIP47	TL031ID	TL034ACN
TIP32B	TIP47G	TL031IP	TL034AID
TIP32BG	TIP48	TL031MD	TL034AIN
TIP32C	TIP48G	TL031MFK	TL034AMD
TIP32CG	TIP49	TL031MJG	TL034AMFK
TIP32G	TIP50	TL031MP	TL034AMJ
TIP33CG	TIP50G	TL032ACD	TL034AMN
TIP35AG	TIS92	TL032ACP	TL034CD
TIP35CG	TIS93	TL032AID	TL034CN
TIP36AG	TIS97	TL032AIP	TL034ID
TIP36B	TIS98	TL032AMD	TL034IN
TIP36CG	TIS99	TL032AMFK	TL034MD

Multisim 14.0 Power Pro Components

TL034MFK	TL051MP	TL054AMJ	TL062ACP
TL034MJ	TL052ACD	TL054AMN	TL062ACPSR
TL034MN	TL052ACP	TL054CD	TL062BCD
TL044CJ	TL052AID	TL054CN	TL062BCP
TL044CN	TL052AIP	TL054ID	TL062CD
TL044MFK	TL052AMD	TL054IN	TL062CP
TL044MJ	TL052AMFK	TL054MD	TL062CPSR
TL044MW	TL052AMJG	TL054MFK	TL062CPW
TL051ACD	TL052AML	TL054MJ	TL062ID
TL051ACP	TL052AMP	TL054MN	TL062IP
TL051AID	TL052CD	TL061ACD	TL062IPW
TL051AIP	TL052CP	TL061ACP	TL062MFK
TL051AMD	TL052ID	TL061BCD	TL062MJG
TL051AMFK	TL052IP	TL061BCP	TL062ML
TL051AMJG	TL052MD	TL061CD	TL062MU
TL051AML	TL052MFK	TL061CP	TL064ACD
TL051AMP	TL052MJG	TL061ID	TL064ACN
TL051CD	TL052ML	TL061IP	TL064BCD
TL051CP	TL052MP	TL061MFK	TL064BCN
TL051ID	TL054ACD	TL061MJG	TL064CD
TL051IP	TL054ACN	TL061ML	TL064CN
TL051MD	TL054AID	TL061MU	TL064CNSR
TL051MFK	TL054AIN	TL061VD	TL064CPW
TL051MJG	TL054AMD	TL061VP	TL064ID
TL051ML	TL054AMFK	TL062ACD	TL064IN

Multisim 14.0 Power Pro Components

TL064MFK	TL071ACP	TL072MJG	TL081AMJG
TL064MJ	TL071BCD	TL072MJGB	TL081BCD
TL064MW	TL071BCP	TL072ML	TL081BCJG
TL066ACD	TL071CD	TL072MP	TL081BCP
TL066ACP	TL071CJG	TL074ACD	TL081CD
TL066CD	TL071CP	TL074ACN	TL081CJG
TL066CP	TL071CPWLE	TL074BCD	TL081CP
TL066ID	TL071ID	TL074BCN	TL081CPW
TL066IP	TL071IP	TL074CD	TL081ID
TL066MFK	TL071MFK	TL074CN	TL081IJG
TL066MJG	TL071MJG	TL074CPWLE	TL081IP
TL070ACD	TL071ML	TL074ID	TL081MFK
TL070ACJG	TL072ACD	TL074IN	TL081MJG
TL070ACP	TL072ACP	TL074MFK	TL081MU
TL070CD	TL072ACPSR	TL074MJ	TL082CD
TL070CJG	TL072BCD	TL074MN	TL082CM
TL070CP	TL072BCP	TL074MW	TL082CP
TL070CPW	TL072CD	TL075	TL082ID
TL070ID	TL072CP	TL075CN	TL082IP
TL070IJG	TL072CPSR	TL080CD	TL082IPWR
TL070IP	TL072CPW	TL080CP	TL082MFK
TL070MD	TL072CPWLE	TL080M	TL082MJG
TL070MP	TL072ID	TL081ACD	TL083
TL071ACD	TL072IP	TL081ACJG	TL084ACD
TL071ACJG	TL072MFK	TL081ACP	TL084ACN

Multisim 14.0 Power Pro Components

TL084ACNSR	TL088IJG	TL322CP	TL431BCLP
TL084BCD	TL088IL	TL322ID	TL431BCP
TL084BCN	TL088IP	TL322IP	TL431CLP
TL084CD	TL088MJG	TL33071D	TL431CP
TL084CN	TL088ML	TL33071P	TL431CPK
TL084CNSR	TL088MU	TL331IDBVR	TL431ID
TL084CPW	TL136	TL331KDBVR	TL431IDBVR
TL084ID	TL136N	TL34071D	TL431IDBZR
TL084IN	TL287CD	TL34071P	TL431ILP
TL084MFK	TL287CJG	TL3472CD	TL431ILPR
TL084MJ	TL287CL	TL3472CP	TL431IP
TL085	TL287CP	TL3472ID	TL431IPK
TL087CD	TL288CD	TL3472IP	TL431QD
TL087CJG	TL288CJG	TL3474CD	TL431QDBVR
TL087CL	TL288CL	TL3474CN	TL431QDBZR
TL087CP	TL288CP	TL3474CPW	TL431QDCKR
TL087ID	TL288MJG	TL3474ID	TL431QPK
TL087IJG	TL288ML	TL3474IN	TL972ID
TL087IL	TL288MU	TL3474IPW	TL972IDGKR
TL087IP	TL321CD	TL35071D	TL972IP
TL088CD	TL321CP	TL35071P	TL972IPW
TL088CJG	TL321ID	TL431ACD	TLC070CD
TL088CL	TL321IP	TL431ACLP	TLC070CP
TL088CP	TL322CD	TL431ACP	TLC070ID
TL088ID	TL322CDR	TL431BCD	TLC070IP

Multisim 14.0 Power Pro Components

TLC071CD	TLC1079MJ	TLC2202BID	TLC2254MW
TLC071CP	TLC1079MN	TLC2202BIP	TLC2262CD
TLC071ID	TLC2201ACD	TLC2202CD	TLC2262CP
TLC071IP	TLC2201ACP	TLC2202CP	TLC2262CPWLE
TLC074CD	TLC2201AID	TLC2202ID	TLC2262MFK
TLC074CN	TLC2201AIP	TLC2202IP	TLC2262MJG
TLC074CPWP	TLC2201BCD	TLC2202MD	TLC2262MU
TLC081CD	TLC2201BCP	TLC2202MFK	TLC2264CD
TLC081CP	TLC2201BID	TLC2202MJG	TLC2264CN
TLC081ID	TLC2201BIP	TLC2202MP	TLC2264CPW
TLC081IP	TLC2201CD	TLC2202Y	TLC2264CPWLE
TLC1078CD	TLC2201CP	TLC2252AID	TLC2264MFK
TLC1078CP	TLC2201ID	TLC2252AIP	TLC2264MJ
TLC1078ID	TLC2201IP	TLC2252AIPWLE	TLC2264MW
TLC1078IP	TLC2201MD	TLC2252CD	TLC2272ACD
TLC1078MD	TLC2201MFK	TLC2252CP	TLC2272ACP
TLC1078MFK	TLC2201MJG	TLC2252CPWLE	TLC2272CD
TLC1078MJG	TLC2201MP	TLC2252MFK	TLC2272CP
TLC1078MP	TLC2201Y	TLC2252MJG	TLC2272CPWLE
TLC1079CD	TLC2202ACD	TLC2252MU	TLC2272Y
TLC1079CN	TLC2202ACP	TLC2254CD	TLC2274ACD
TLC1079ID	TLC2202AID	TLC2254CN	TLC2274ACN
TLC1079IN	TLC2202AIP	TLC2254CPWLE	TLC2274ACPW
TLC1079MD	TLC2202BCD	TLC2254MFK	TLC2274CD
TLC1079MFK	TLC2202BCP	TLC2254MJ	TLC2274CN

Multisim 14.0 Power Pro Components

TLC2274CPWLE	TLC254CD	TLC2652AIN	TLC2654AC-14D
TLC2274MD	TLC254CN	TLC2652AIP	TLC2654AC-8D
TLC2274MFK	TLC254CPW	TLC2652AM-14D	TLC2654ACN
TLC2274MJ	TLC25L2ACD	TLC2652AM-8D	TLC2654ACP
TLC2274MN	TLC25L2ACP	TLC2652AMFK	TLC2654AI-14D
TLC251ACD	TLC25L2BCD	TLC2652AMJ	TLC2654AID
TLC251ACP	TLC25L2BCP	TLC2652AMJG	TLC2654AIN
TLC251BCD	TLC25L2CD	TLC2652AMN	TLC2654AIP
TLC251BCP	TLC25L2CP	TLC2652AMP	TLC2654AM-14D
TLC251CD	TLC25L4CD	TLC2652C-14D	TLC2654AM-8D
TLC251CP	TLC25L4CN	TLC2652C-8D	TLC2654AMF
TLC251Y	TLC25M2ACD	TLC2652CN	TLC2654AMFK
TLC252ACD	TLC25M2ACP	TLC2652CP	TLC2654AMJ
TLC252ACP	TLC25M2BCD	TLC2652I-14D	TLC2654AMJG
TLC252ACPW	TLC25M2BCP	TLC2652ID	TLC2654AMN
TLC252BCD	TLC25M2CD	TLC2652IN	TLC2654AMP
TLC252BCP	TLC25M2CP	TLC2652IP	TLC2654C-14D
TLC252BCPW	TLC25M4CD	TLC2652M-14D	TLC2654C-8D
TLC252CD	TLC25M4CN	TLC2652M-8D	TLC2654CN
TLC252CP	TLC2652AC-14D	TLC2652MFK	TLC2654CP
TLC252CPW	TLC2652AC-8D	TLC2652MJ	TLC2654I-14D
TLC254ACD	TLC2652ACN	TLC2652MJG	TLC2654I-8D
TLC254ACN	TLC2652ACP	TLC2652MN	TLC2654IN
TLC254BCD	TLC2652AI-14D	TLC2652MP	TLC2654IP
TLC254BCN	TLC2652AI-8D	TLC2652Y	TLC2654M-14D

Multisim 14.0 Power Pro Components

TLC2654M-8D	TLC272ID	TLC279ID	TLC27L4AIN
TLC2654MFK	TLC272IP	TLC279IN	TLC27L4BCD
TLC2654MJ	TLC272MD	TLC279MD	TLC27L4BCN
TLC2654MJG	TLC272MFK	TLC279MFK	TLC27L4BID
TLC2654MN	TLC272MJG	TLC279MJ	TLC27L4BIN
TLC2654MP	TLC272MP	TLC279MN	TLC27L4CD
TLC271ACD	TLC274CD	TLC27L2ACD	TLC27L4CN
TLC271ACP	TLC274CN	TLC27L2ACP	TLC27L4ID
TLC271AID	TLC274CPW	TLC27L2AID	TLC27L4IN
TLC271AIP	TLC274ID	TLC27L2AIP	TLC27L4MD
TLC271BCD	TLC274IN	TLC27L2BCD	TLC27L4MFK
TLC271BCP	TLC274MD	TLC27L2BCP	TLC27L4MJ
TLC271BID	TLC274MFK	TLC27L2BID	TLC27L4MN
TLC271BIP	TLC274MJ	TLC27L2BIP	TLC27L7CD
TLC271CD	TLC274MN	TLC27L2CD	TLC27L7CP
TLC271CP	TLC277CD	TLC27L2CP	TLC27L7ID
TLC271ID	TLC277CP	TLC27L2ID	TLC27L7IP
TLC271IP	TLC277ID	TLC27L2IP	TLC27L7MD
TLC271MD	TLC277IP	TLC27L2MD	TLC27L7MFK
TLC271MFK	TLC277MD	TLC27L2MFK	TLC27L7MJG
TLC271MJG	TLC277MFK	TLC27L2MJG	TLC27L7MP
TLC271MP	TLC277MJG	TLC27L2MP	TLC27L9CD
TLC272CD	TLC277MP	TLC27L4ACD	TLC27L9CN
TLC272CP	TLC279CD	TLC27L4ACN	TLC27L9ID
TLC272CPW	TLC279CN	TLC27L4AID	TLC27L9IN

Multisim 14.0 Power Pro Components

TLC27L9MD	TLC27M4BCN	TLC27M9MJ	TLC3702ID
TLC27L9MFK	TLC27M4BID	TLC27M9MN	TLC3702IP
TLC27L9MJ	TLC27M4BIN	TLC339CD	TLC3702MD
TLC27L9MP	TLC27M4CD	TLC339CN	TLC3702MFK
TLC27M2ACD	TLC27M4CN	TLC339ID	TLC3702MJG
TLC27M2ACP	TLC27M4ID	TLC339IN	TLC3702QJG
TLC27M2AID	TLC27M4IN	TLC339MD	TLC3704CD
TLC27M2AIP	TLC27M4MD	TLC339MN	TLC3704CN
TLC27M2BCD	TLC27M4MFK	TLC339QD	TLC3704CPW
TLC27M2BCP	TLC27M4MJ	TLC339QN	TLC3704ID
TLC27M2BID	TLC27M4MN	TLC352CD	TLC3704IN
TLC27M2BIP	TLC27M7CD	TLC352CP	TLC3704MFK
TLC27M2CD	TLC27M7CP	TLC352ID	TLC3704MJ
TLC27M2CP	TLC27M7ID	TLC352IP	TLC3704QJ
TLC27M2ID	TLC27M7IP	TLC352MFK	TLC372CD
TLC27M2IP	TLC27M7MD	TLC352MJG	TLC372CP
TLC27M2MD	TLC27M7MFK	TLC354CD	TLC372CPW
TLC27M2MFK	TLC27M7MJG	TLC354CN	TLC372ID
TLC27M2MJG	TLC27M7MP	TLC354CPW	TLC372IP
TLC27M2MP	TLC27M9CD	TLC354ID	TLC372MD
TLC27M4ACD	TLC27M9CN	TLC354IN	TLC372MFK
TLC27M4ACN	TLC27M9ID	TLC354MD	TLC372MJG
TLC27M4AID	TLC27M9IN	TLC354MN	TLC372MP
TLC27M4AIN	TLC27M9MD	TLC3702CD	TLC372QD
TLC27M4BCD	TLC27M9MFK	TLC3702CP	TLC372QP

Multisim 14.0 Power Pro Components

TLC374CD	TLC552CD	TLE2021CP	TLE2024ACN
TLC374CN	TLC552CN	TLE2021CPWLE	TLE2024AIDW
TLC374CPW	TLC555CD	TLE2021ID	TLE2024AIN
TLC374ID	TLC555CP	TLE2021IP	TLE2024AMDW
TLC374IN	TLC555CPSR	TLE2021MD	TLE2024AMFK
TLC374MD	TLC555CPW	TLE2021MFK	TLE2024AMJ
TLC374MFK	TLC555ID	TLE2021MJG	TLE2024AMN
TLC374MJ	TLC555IP	TLE2021MP	TLE2024BCDW
TLC374MN	TLC555QDR	TLE2021Y	TLE2024BCN
TLC374QD	TLC556CD	TLE2022ACD	TLE2024BIDW
TLC374QN	TLC556CN	TLE2022ACP	TLE2024BIN
TLC393CD	TLC556ID	TLE2022AID	TLE2024BMDW
TLC393CP	TLC556IN	TLE2022AIP	TLE2024BMJ
TLC393CPWLE	TLE2021ACD	TLE2022BCD	TLE2024BMN
TLC393ID	TLE2021ACP	TLE2022BCP	TLE2024CDW
TLC393IP	TLE2021AID	TLE2022BID	TLE2024CN
TLC393IPWLE	TLE2021AIP	TLE2022BIP	TLE2024IDW
TLC393MD	TLE2021AMD	TLE2022CD	TLE2024IN
TLC393MFK	TLE2021AMFK	TLE2022CDBLE	TLE2024MDW
TLC393MJG	TLE2021AMJG	TLE2022CP	TLE2024MFK
TLC393MP	TLE2021AMP	TLE2022CPWLE	TLE2024MJ
TLC393QD	TLE2021BI	TLE2022ID	TLE2024MN
TLC551CD	TLE2021BMJG	TLE2022IP	TLE2024Y
TLC551CP	TLE2021CD	TLE2022Y	TLE2027ACD
TLC552C	TLE2021CDBLE	TLE2024ACDW	TLE2027ACP

Multisim 14.0 Power Pro Components

TLE2027AID	TLE2037CD	TLE2061BMP	TLE2062BID
TLE2027AIP	TLE2037CP	TLE2061CD	TLE2062BIP
TLE2027AMD	TLE2037ID	TLE2061CDBLE	TLE2062BMD
TLE2027AMFK	TLE2037IP	TLE2061CL	TLE2062BMFK
TLE2027AMJG	TLE2037MD	TLE2061CP	TLE2062BMJG
TLE2027AML	TLE2037MFK	TLE2061CPWLE	TLE2062BMP
TLE2027AMP	TLE2037MJG	TLE2061ID	TLE2062CD
TLE2027CD	TLE2037ML	TLE2061IL	TLE2062CP
TLE2027CP	TLE2037MP	TLE2061IP	TLE2062ID
TLE2027ID	TLE2061ACD	TLE2061MD	TLE2062IP
TLE2027IP	TLE2061ACL	TLE2061MFK	TLE2062MD
TLE2027MD	TLE2061ACP	TLE2061MJG	TLE2062MFK
TLE2027MFK	TLE2061AID	TLE2061ML	TLE2062MJG
TLE2027MJG	TLE2061AIL	TLE2061MP	TLE2062MP
TLE2027ML	TLE2061AIP	TLE2061Y	TLE2062Y
TLE2027MP	TLE2061AMD	TLE2062ACD	TLE2064ACD
TLE2037ACD	TLE2061AMFK	TLE2062ACP	TLE2064ACN
TLE2037ACP	TLE2061AMJG	TLE2062AID	TLE2064AID
TLE2037AID	TLE2061AML	TLE2062AIP	TLE2064AIN
TLE2037AIP	TLE2061AMP	TLE2062AMD	TLE2064AMD
TLE2037AMD	TLE2061BCL	TLE2062AMFK	TLE2064AMFK
TLE2037AMFK	TLE2061BIL	TLE2062AMJG	TLE2064AMJ
TLE2037AMJG	TLE2061BIP	TLE2062AMP	TLE2064AMN
TLE2037AML	TLE2061BMJG	TLE2062BCD	TLE2064BCN
TLE2037AMP	TLE2061BML	TLE2062BCP	TLE2064BIN

Multisim 14.0 Power Pro Components

TLE2064BMJ	TLE2081MJG	TLE2141AMD	TLE2142MD
TLE2064BMN	TLE2082ACD	TLE2141AMFK	TLE2142MFK
TLE2064CD	TLE2082ACP	TLE2141AMJG	TLE2142MJG
TLE2064CN	TLE2082AID	TLE2141AMP	TLE2142MP
TLE2064ID	TLE2082AIP	TLE2141CD	TLE2142Y
TLE2064IN	TLE2082AMD	TLE2141CP	TLE2144ACN
TLE2064MD	TLE2082AMFK	TLE2141ID	TLE2144AIN
TLE2064MFK	TLE2082AMJG	TLE2141IP	TLE2144AMFK
TLE2064MJ	TLE2082AMP	TLE2141MD	TLE2144AMJ
TLE2064MN	TLE2082CD	TLE2141MFK	TLE2144AMN
TLE2064Y	TLE2082CP	TLE2141MJG	TLE2144CDW
TLE2071CD	TLE2082ID	TLE2141MP	TLE2144CN
TLE2071CP	TLE2082IP	TLE2141Y	TLE2144IDW
TLE2071MFK	TLE2082MD	TLE2142ACD	TLE2144IN
TLE2071MJG	TLE2082MFK	TLE2142ACP	TLE2144MDW
TLE2072CD	TLE2082MJG	TLE2142AID	TLE2144MFK
TLE2072CP	TLE2082MP	TLE2142AIP	TLE2144MJ
TLE2072MFK	TLE2084CDW	TLE2142AMD	TLE2144MN
TLE2074CDW	TLE2084CN	TLE2142AMFK	TLE2144Y
TLE2074CN	TLE2084MFK	TLE2142AMJG	TLE2161ACD
TLE2074MFK	TLE2084MJ	TLE2142AMP	TLE2161ACP
TLE2074MJ	TLE2141ACD	TLE2142CD	TLE2161AID
TLE2081CD	TLE2141ACP	TLE2142CP	TLE2161AIP
TLE2081CP	TLE2141AID	TLE2142ID	TLE2161AMD
TLE2081MFK	TLE2141AIP	TLE2142IP	TLE2161AMFK

Multisim 14.0 Power Pro Components

TLE2161AMJG	TLE2426CD	TLV2254MJ	TLV2341ID
TLE2161AML	TLE2426IP	TLV2254QD	TLV2341IP
TLE2161AMP	TL-OP	TLV2262AIPWLE	TLV2341IPWLE
TLE2161BCP	TL-OP1	TLV2262ID	TLV2342ID
TLE2161BIP	TLP521-1	TLV2262IP	TLV2342IP
TLE2161BMJ	TLP521-2	TLV2262MFK	TLV2342IPWLE
TLE2161BML	TLP521-3	TLV2262MJG	TLV2344ID
TLE2161BMP	TLP521-4	TLV2262MU	TLV2344IN
TLE2161CD	TLV2211CDBV	TLV2264AIPWLE	TLV2344IPWLE
TLE2161CP	TLV2211IDBV	TLV2264ID	TLV2352ID
TLE2161ID	TLV2221CDBV	TLV2264IN	TLV2352IP
TLE2161IP	TLV2221IDBV	TLV2264MJ	TLV2352IPW
TLE2161MD	TLV2231CDBV	TLV2264QD	TLV2352IPWLE
TLE2161MFK	TLV2231IDBV	TLV2322ID	TLV2354ID
TLE2161MJG	TLV2252ID	TLV2322IP	TLV2354IN
TLE2161ML	TLV2252IP	TLV2322IPWLE	TLV2354IPW
TLE2161MP	TLV2252MFK	TLV2324ID	TLV2354MJ
TLE2227ACP	TLV2252MJG	TLV2324IN	TLV2361CDBV
TLE2227CDW	TLV2252MU	TLV2324IPWLE	TLV2361IDBV
TLE2227CP	TLV2254AID	TLV2332ID	TLV2362ID
TLE2237ACP	TLV2254AIN	TLV2332IP	TLV2362IDGK
TLE2237CDW	TLV2254AIPWLE	TLV2332IPWLE	TLV2362IP
TLE2237CP	TLV2254ID	TLV2334ID	TLV2362IPS
TLE2425CD	TLV2254IN	TLV2334IN	TLV2362IPW
TLE2425ID	TLV2254MFK	TLV2334IPWLE	TLV2370ID

Multisim 14.0 Power Pro Components

TLV2370IDBV	TLV2402IDGK	TLV2455AID	TLV271ID
TLV2370IP	TLV2402IP	TLV2455AIN	TLV271IDBVR
TLV2371ID	TLV2432AID	TLV2455AIPW	TLV271IP
TLV2371IDBV	TLV2432AIPW	TLV2460CD	TLV272CD
TLV2371IP	TLV2432AMJG	TLV2460CDBV	TLV272CDGK
TLV2372ID	TLV2434AID	TLV2460CP	TLV272ID
TLV2372IDGK	TLV2434AIPW	TLV2461CD	TLV272IDGK
TLV2372IP	TLV2442CD	TLV2461CDBV	TLV272IP
TLV2373ID	TLV2442CPW	TLV2461CP	TLV274CD
TLV2373IDGS	TLV2442MJG	TLV2470AID	TLV274CPW
TLV2373IN	TLV2444CD	TLV2470AIP	TLV274ID
TLV2374ID	TLV2444CPW	TLV2471AID	TLV274IN
TLV2374IN	TLV2444ID	TLV2471AIP	TLV274IPW
TLV2374IPW	TLV2444IPW	TLV2472AID	TLV2760ID
TLV2375ID	TLV2450AID	TLV2472AIP	TLV2760IDBV
TLV2375IN	TLV2450AIP	TLV2473AID	TLV2760IP
TLV2375IPW	TLV2451AID	TLV2473AIP	TLV2761ID
TLV2401CD	TLV2451AIP	TLV2474AID	TLV2761IDBV
TLV2401CDBV	TLV2452AID	TLV2474AIN	TLV2761IP
TLV2401ID	TLV2452AIP	TLV2474AIPWP	TLV2762ID
TLV2401IDBV	TLV2453AID	TLV2475AID	TLV2762IDGK
TLV2401IP	TLV2453AIN	TLV2475AIN	TLV2762IP
TLV2402CD	TLV2454AID	TLV2475AIPWP	TLV2763ID
TLV2402CDGK	TLV2454AIN	TLV271CD	TLV2763IDGS
TLV2402ID	TLV2454AIPW	TLV271CDBVR	TLV2763IN

Multisim 14.0 Power Pro Components

TLV2764ID	TLV3401IDG4	TLV4112ID	TLVH431IDCKR
TLV2764IN	TLV3401IP	TLV4112IDGN	TLVH431ILP
TLV2764IPW	TLV342ID	TLV4112IP	TLVH431ILPR
TLV2765ID	TLV342IDGKR	TLV4113CDGQR	TLVH431IPK
TLV2765IN	TLV342IRUGR	TLV4113ID	TLVH431QDBVR
TLV2765IPW	TLV3491	TLV4113IDGQ	TLVH431QDBZR
TLV2772CD	TLV3501AID	TLV4113IN	TLVH431QDCKR
TLV2772CDGK	TLV3501AIDBVR	TLV431CDBVR	TLVH431QLP
TLV2772CP	TLV3691IDCKR	TLV431CDBZR	TLVH431QLPR
TLV2782AID	TLV3691IDPFR	TLV431CLP	TLVH431QPK
TLV2783AID	TLV3701CD	TLV431CLPM	TMP20AIDCKR
TLV2784AID	TLV3701CDBVR	TLV431CLPR	TMP20AIDRLR
TLV2784AIPW	TLV3701ID	TLV431IDBVR	TMP90C800F
TLV2785AID	TLV3701IDBVR	TLV431IDBZR	TMP90C800N
TLV2785AIPW	TLV3701IP	TLV431ILP	TMP90C801F
TLV3012AIDBVR	TLV4110ID	TLV431ILPR	TMP90C801N
TLV3012AIDCKR	TLV4110IDGNR	TLV431QPK	TMP94CM40F
TLV3201AIDBVR	TLV4110IP	TLVH431CDBVR	TMS320C6711B-100GFNA
TLV3201AIDCKR	TLV4111CD	TLVH431CDBZR	TMS320LC2402A-PAG(64)
TLV3202AID	TLV4111CDGN	TLVH431CDCKR	TMS320LC2402A-PG(64)
TLV3202AIDGK	TLV4111ID	TLVH431CLP	TMS320LC2404A-PZ(100)
TLV3401CD	TLV4111IDGN	TLVH431CLPR	TMS320LC2406A-PZ(100)
TLV3401CDBVR	TLV4112CD	TLVH431CPK	
TLV3401ID	TLV4112CDGN	TLVH431IDBVR	
TLV3401IDBVR	TLV4112CP	TLVH431IDBZR	

Multisim 14.0 Power Pro Components

TMS320LF2402A-PG(64)	TPS2828_SOT23_5	TPSMA30AHE3/61T	TRANSFER_FUNCTION_BLOCK
TMS320LF2403A-PAG(64)	TPS2829_SOT23_5	TPSMA33AHE3/61T	TRANSFORMER_CT_RATED
TMS320LF2406A-PZ(100)	TPS2830_SO14	TPSMA36AHE3/5AT	TRANSFORMER_RATED
TMS320LF2407A-PGE(144)	TPS2831_SO14	TPSMB24AHE3/52T	TRANSISTOR
TN2219	TPS2832_SO8	TPSMB27A/2	TRANSISTOR_DELAY
TN2219A	TPS2833_SO8	TPSMB30AHE3/52T	TRANSISTOR_DIODE
TN2905	TPS2834_SO14	TPSMB33AHE3/52T	TRANSISTOR_DIODE_DELAY
TN2905A	TPS2835_SO14	TPSMB36A/5T	TRANSPORT_DELAY
TN4036	TPS2836_SO8	TPSMB39A-E3/2T	TRF37A75IDSGR
TOSHIBA-MIPS-HDR	TPS2837_SO8	TPSMC22A-E3/57T	TRF37B75IDSGR
TPA301D	TPS2838_SO16	TPSMC27A-E3/57T	TRF37C75IDSGR
TPA301DGN	TPS2839_SO16	TPSMC30AHE3_A/H	TRIAC
TPA301DR	TPS2848_SO14	TPSMC33A-E3/51T	TRIANGULAR_CURRENT
TPS2811_SO8	TPS2849_SO14	TPSMC36A/9AT	TRIANGULAR_VOLTAGE
TPS2812_SO8	TPS5300_SO32	TPSMC39A-E3/57T	TRIODE_VIRTUAL
TPS2813_SO8	TPS60240_SO8	TPSMP18AHM3/84A	TRISTATE
TPS2814_SO8	TPS60241_SO8	TPSMP24AHM3/84A	TRISTATE_NEG
TPS2815_SO8	TPS60242_SO8	TPSMP27AHE3/84A	TS_VIRTUAL
TPS2816_SOT23_5	TPS60243_SO8	TPSMP30AHM3/84A	TVP5145PFP-TQFP(80)
TPS2817_SOT23_5	TPS76150DBVR	TPSMP36AHM3/84A	
TPS2818_SOT23_5	TPS780230300DRV	TRAFFIC_LIGHT	
TPS2819_SOT23_5	TPSMA16AHE3/61T	TRAFFIC_LIGHT_SINGLE	
	TPSMA20A/11T		
	TPSMA27AHE3/61T		

Multisim 14.0 Power Pro Components

U257	UA723CD	UC2705_DIP8	UC3842T_SO8
U290	UA723CFK	UC2842A_DIP8	UC3843A_DIP8
U291	UA723CJ	UC2842A_SO8	UC3843A_SO8
U308	UA723CN	UC2842B_DIP8	UC3843B_DIP8
U309	UA723MU	UC2842B_SO8	UC3843B_SO8
U310	UA741CD	UC2843A_DIP8	UC3843T_DIP8
U401	UA741CP	UC2843A_SO8	UC3843T_SO8
U402	UA741MFK	UC2843B_DIP8	UC3844A_DIP8
U403	UA741MJ	UC2843B_SO8	UC3844A_SO8
U404	UA741MJG	UC2844A_DIP8	UC3844B_DIP8
U405	UA741MU	UC2844A_SO8	UC3844B_SO8
U406	UA747CD	UC2844B_DIP8	UC3844T_DIP8
U430	UA747CN	UC2844B_SO8	UC3844T_SO8
U440	UA747MFK	UC2845A_DIP8	UC3845A_DIP8
U441	UA747MJ	UC2845A_SO8	UC3845A_SO8
UA709AMJ	UA747MW	UC2845B_DIP8	UC3845B_DIP8
UA709AMJG	UA748CD	UC2845B_SO8	UC3845B_SO8
UA709AMU	UA748CP	UC3248	UC3845T_DIP8
UA709AMW	UA748JG	UC3705_DIP8	UC3845T_SO8
UA709CD	UA748MJG	UC3842	UCC27323_SO8
UA709CJG	UA748MU	UC3842A_DIP8	UCC27324_SO8
UA709CP	UAF42AP	UC3842A_SO8	UCC27325_SO8
UA709MJ	UAF42AU	UC3842B_DIP8	UCC37323_SO8
UA709MU	UC1705	UC3842B_SO8	UCC37324_SO8
UA709MW	UC1705_DIP8	UC3842T_DIP8	UCC37325_SO8

Multisim 14.0 Power Pro Components

UF4002-E3/54	UPC2610H	V_REF1	VARIRES
UF4007-E3/54	uPC277C	V_REF2	VBP104FAS
UF5406-E3/54	uPC277D	V_REF3	VBP104FASR
UG06D-E3/54	uPC277G	V_REF4	VBPW34FAS
UG1D-E3/54	uPC339C	V_REF5	VBPW34FASR
UG30DPT-E3/45	uPC339G	V10P10-M3/86A	VBPW34S
UG5JT-E3/45	uPC339G2	V12P10-M3/86A	VBPW34SR
UG8DT-E3/45	uPC393C	V18MA1A	VC121030H620
UG8JCT-E3/45	uPC393G2	V430MA7B	VCA610P
UG8JTHER3/45	uPC393HA	V8P10HM3/86A	VCA610PA
ULN2001_DIP16	UPC7893A	VARIABLE_CAPACIT OR	VCA610U
ULN2001_SO16	UPC78N10H	VARIABLE_CAPACIT OR_RATED	VCA610UA
ULN2002_DIP16	UPC7905	VARIABLE_CAPACIT OR_VIRTUAL	VCA810AID
ULN2002_SO16	UPC7908	VARIABLE_INDUCT OR	VCA810ID
ULN2003_DIP16	UPC7912	VARIABLE_INDUCT OR_VIRTUAL	VCA821ID
ULN2003_SO16	UPC7915	VARIABLE_INDUCT OR_RATED	VCA824ID
ULN2004_DIP16	UPC7918	VARIABLE_INDUCT OR_VIRTUAL	VCA8500IRGCR
ULN2004_SO16	UPC7924	VARIABLE_PULLUP_ VIRTUAL	VCC
UNDCD_BARGRAPH	US1G-E3/61T	VARIABLE_RESISTO R_VIRTUAL	VCR2N
UPA1427H	US1J-E3/5AT	VARIABLE_RESISTO R_VIRTUAL	VDAC
uPC177C	US1M-E3/61T	VARIABLE_RESISTO R_VIRTUAL	VDAC16
uPC177ED	USER_MOSFET_3TE N	VARIABLE_RESISTO R_VIRTUAL	VDD
uPC177G	UVLO	VARIABLE_RESISTO R_VIRTUAL	VEE
UPC2407HF	UX60-MB-5ST	VARICAP	VN0300L
UPC2410HF		VARICOIL	VN0300M

Multisim 14.0 Power Pro Components

VN0606M	VO0631T	VO615A-3X006	VOLTAGE_CONTROLLED_SPDT
VN0610L	VO0631-X001T	VO615A-3X007T	VOLTAGE_CONTROLLED_SPST
VN0610LL	VO0661T	VO615A-3X008T	VOLTAGE_CONTROLLED_SPST_ANIMATED
VN0808M	VO2601	VO615A-3X009T	VOLTAGE_CONTROLLED_SPST_BOUNC E
VN10KE	VO2601-X006	VO615A-3X016	VOLTAGE_CONTROLLED_SQUARE_WA VE
VN10KM	VO2601-X007T	VO615A-3X017T	VOLTAGE_CONTROLLED_TRIANGLE_W AVE
VN10LF	VO2601-X016	VO615A-3X018T	VOLTAGE_CONTROLLED_VOLTAGE_SO URCE
VN10LM	VO2601-X017T	VO615A-3X019T	VOLTAGE_CONTROLLED_INDUCTOR_VI RTUAL
VN1210M	VO2611	VOLTAGE_CONTROLLED_CAPACITOR_ VIRTUAL	VOLTAGE_GAIN_BLOCK
VN2010L	VO2611-X006	VOLTAGE_CONTROLLED_CURRENT_SO URCE	VOLTAGE_HYSTERE SIS_BLOCK
VN2222L	VO2611-X007T	VOLTAGE_CONTROLLED_DPDT	VOLTAGE_INTEGRA TOR
VN2222LL	VO2611-X016	VOLTAGE_CONTROLLED_LIMITER	VOLTAGE_LIMITER
VN2222LM	VO2611-X017T	VOLTAGE_CONTROLLED_PIECEWISE_LI NEAR_SOURCE	VOLTAGE_SLEW_R ATE_BLOCK
VN2406L	VO2630	VOLTAGE_CONTROLLED_RESISTOR_VI RTUAL	VOLTAGE_SUMMER
VN2406M	VO2630-X006	VOLTAGE_CONTROLLED_SINE_WAVE	
VN2410L	VO2630-X007T		
VN2410M	VO2631		
VN4012L	VO2631-X006		
VN46AFD	VO2631-X007T		
VN88AFD	VO2631-X017T		
VO0600T	VO4661		
VO0601T	VO4661-X006		
VO0601-X001T	VO4661-X007T		
VO0611T	VO615A-3		
VO0630T	VO615A-3X001		

Multisim 14.0 Power Pro Components

VOLTAGE_TRIGGER	XC3042L-VQ100	XC5202-6VQ64C	XC5210-3PC84C
ED_PIECEWISE_LINEAR_SOURCE	XC3120A-PQ100	XC5204-3PC84C	XC5210-3TQ144C
VOLTMETER_H	XC3130A-PQ100	XC5204-3PQ100C	XC5210-4PC84C
VOLTMETER_HR	XC3130A-VQ100	XC5204-3TQ144C	XC5210-4TQ144C
VOLTMETER_V	XC3142A-PQ100	XC5204-4PC84C	XC5210-5PC84C
VOLTMETER_VR	XC3142A-VQ100	XC5204-4PQ100C	XC5210-5TQ144C
VOM452T	XC3142L-VQ100	XC5204-4TQ144C	XC5210-6PC84C
VOM453T	XC4002XL-1PC84C	XC5204-5PC84C	XC5210-6TQ144C
VP0610L	XC4002XL-2PC84C	XC5204-5PQ100C	XC5215-3PQ160C
VP0808L	XC4002XL-3PC84C	XC5204-5TQ144C	XC5215-4PQ160C
VP0808M	XC5202-3PC84C	XC5204-6PC84C	XC5215-5PQ160C
VP1008L	XC5202-3PQ100C	XC5204-6PQ100C	XC5215-6PQ160C
VQ1000J	XC5202-3TQ144C	XC5204-6TQ144C	XC9572XL-10TQ100C
VQ1001J	XC5202-3VQ64C	XC5206-3PC84C	XC9572XL-7TQ100C
VSS	XC5202-4PC84C	XC5206-3PQ100C	XC9572XL-7TQ100C
VTERM	XC5202-4PQ100C	XC5206-3TQ144C	XCS05-3PC84C
W06G-E4/51	XC5202-4TQ144C	XC5206-4PC84C	XCS05-4PC84C
WE300B	XC5202-4VQ64C	XC5206-4PQ100C	XCS05XL-4PC84C
WOBBLE_STICK	XC5202-5PC84C	XC5206-4TQ144C	XCS10-3PC84C
XC3020A-PQ100	XC5202-5PQ100C	XC5206-5PC84C	XCS10-4PC84C
XC3030A-PQ100	XC5202-5TQ144C	XC5206-5PQ100C	XCS10XL-4PC84C
XC3030A-VQ100	XC5202-5VQ64C	XC5206-5TQ144C	XCS20-3VQ100C
XC3030L-VQ100	XC5202-6PC84C	XC5206-6PC84C	XCS20-4VQ100C
XC3042A-PQ100	XC5202-6PQ100C	XC5206-6PQ100C	XCS20XL-4VQ100C
XC3042A-VQ100	XC5202-6TQ144C	XC5206-6TQ144C	XCS30-3VQ100C

Multisim 14.0 Power Pro Components

XCS30-4VQ100C	XOR4	Z4KE160A	Z84C20-PLCC(44)
XCS30XL-4VQ100C	XOR4	Z4KE170	Z84C30-DIP(28)
XCS40-4PQ208C	XOR5	Z4KE170A	Z84C30-PLCC(44)
XCS40XL-4PQ208C	XOR5	Z4KE180	Z84C30-QFP(44)
XILINX-PARALLEL- III-IV-HDR	XOR6	Z4KE180A	Z84C40-DIP(40)
	XOR6	Z4KE190	Z84C41-DIP(40)
XILINX-PARALLEL- IV-HDR	XOR7	Z4KE190A	Z84C42-DIP(40)
	XOR7	Z4KE200	Z84C43-QFP(44)
XNOR2	XOR8	Z4KE200A	Z84C44-PLCC(44)
XNOR2	XOR8	Z80180-DIP(64)	Z84C90-LQFP(100)
XNOR3	XTR300AIRGWR	Z80180-PLCC(68)	Z84C90-PLCC(84)
XNOR3	Z08470-DIP(40)	Z80180-QFP(80)	Z8L180-DIP(64)
XNOR4	Z4KE100	Z80181-QFP(100)	Z8L180-PLCC(68)
XNOR4	Z4KE100A	Z80182-QFP(100)	Z8L180-QFP(80)
XNOR5	Z4KE110	Z80182-VQFP(100)	Z8L182-QFP(100)
XNOR5	Z4KE110A	Z80195-QFP(100)	Z8L182-VQFP(100)
XNOR6	Z4KE120	Z84015-QFP(100)	Z8S180-DIP(64)
XNOR6	Z4KE120A	Z84C00-DIP(40)	Z8S180-PLCC(68)
XNOR7	Z4KE130	Z84C00-PLCC(44)	Z8S180-QFP(80)
XNOR7	Z4KE130A	Z84C00-QFP(44)	ZC820
XNOR8	Z4KE140	Z84C10-DIP(40)	ZC821
XNOR8	Z4KE140A	Z84C10-PLCC(44)	ZC822
XOR2	Z4KE150	Z84C15-QFP(100)	ZC823
XOR2	Z4KE150A	Z84C15-VQFP(100)	ZC824
XOR3	Z4KE160	Z84C20-DIP(40)	ZC825

Multisim 14.0 Power Pro Components

ZC826	ZPD10	ZTX1047A	ZTX239
ZC830A	ZPD11	ZTX1048A	ZTX239B
ZC831A	ZPD12	ZTX1049A	ZTX320
ZC832A	ZPD13	ZTX1051A	ZTX321
ZC833A	ZPD15	ZTX1053A	ZTX325
ZC834A	ZPD16	ZTX1055A	ZTX327
ZC835A	ZPD18	ZTX107	ZTX337A
ZC836A	ZPD2.7	ZTX107B	ZTX338A
ZDX1F	ZPD20	ZTX108	ZTX360
ZDX2F	ZPD22	ZTX108B	ZTX450
ZDX5	ZPD24	ZTX109	ZTX454
ZENER	ZPD27	ZTX109B	ZTX455
ZGL41_100	ZPD3.0	ZTX1147A	ZTX458
ZGL41_110	ZPD3.3	ZTX1149A	ZTX549
ZGL41_120	ZPD3.6	ZTX1151A	ZTX550
ZGL41_130	ZPD3.9	ZTX212	ZTX558
ZGL41_140	ZPD30	ZTX212A	ZTX601B
ZGL41_150	ZPD33	ZTX213	ZTX604
ZGL41_160	ZPD4.3	ZTX213A	ZTX605
ZGL41_170	ZPD4.7	ZTX214	ZTX614
ZGL41_180	ZPD5.1	ZTX214A	ZTX618
ZGL41_190	ZPD6.2	ZTX237	ZTX649
ZGL41_200	ZPD6.8	ZTX237B	ZTX650
ZHCS1000	ZPD7.5	ZTX238	ZTX651
ZHCS750	ZPD8.2	ZTX238B	ZTX653

Multisim 14.0 Power Pro Components

ZTX657	ZTX851	ZVP3306F
ZTX658	ZTX857	ZVP4424A
ZTX688B	ZTX869	ZVP4424G
ZTX689B	ZTX948	
ZTX690B	ZTX949	
ZTX692B	ZTX951	
ZTX694B	ZTX953	
ZTX696B	ZTX955	
ZTX704	ZTX956	
ZTX705	ZTX957	
ZTX718	ZTX958	
ZTX749	ZTX968	
ZTX750	ZVN0124A	
ZTX751	ZVN2106A	
ZTX753	ZVN2106G	
ZTX757	ZVN3306A	
ZTX758	ZVN3306F	
ZTX788A	ZVN3310F	
ZTX788B	ZVN4210G	
ZTX789A	ZVN4306G	
ZTX790A	ZVN4310G	
ZTX792A	ZVN4424G	
ZTX795A	ZVP2106A	
ZTX796A	ZVP2106G	
ZTX849	ZVP3306	