NI PXIe-4353 Specifications

Français Deutsch 日本語 한국어 简体中文 ni.com/manuals

This document lists specifications for the NI PXIe-4353 module. These specifications are typical for the range of 0 $^{\circ}$ C to 55 $^{\circ}$ C unless otherwise stated. The system must be allowed to warm up for 15 minutes to achieve the rated accuracy. All specifications are subject to change without notice. Visit ni.com/manuals for the most current specifications and product documentation.



Note Keep the filler panels on all unused slots in your chassis to maintain forced air cooling.

Thermocouple Measurement Accuracy

Туре	-100 °C to 0 °C*	-100 °C to 0 °C* 0 °C to 300 °C*		900 °C to 1400 °C*	
J/N	0.47 °C	0.35 °C	0.47 °C	0.56 °C	
K	0.44 °C	0.38 °C	0.58 °C	0.88 °C	
T/E	0.48 °C	0.32 °C	0.48 °C	_	
R/S	_	0.81 °C	0.60 °C	0.70 °C	
В	_	_	1.00 °C	0.49 °C	

^{*} The values in this table are typical for 23 °C ±5 °C when using the module with a TB-4353 in the High-Resolution ADC-timing mode. For detailed accuracy tables, including maximum specifications, refer to the *Temperature Measurement Accuracy* section.

Input Characteristics

Number of channels	. 32 thermocouple channels, 2 autozero channels, 8 cold-junction compensation channels
ADC resolution	24 bits
Type of ADC	Delta-Sigma
Sampling mode	Scanned
Maximum sample rate	. 90 S/s (Refer to the <i>Timing</i> section for more details.)
Voltage measurement range	±80 mV



Temperature measurement range	. Full NIST temperature range (J, K, T, E, N, B, R, S thermocouple types)
50/60 Hz noise rejection (High resolution mode)	.70 dB
Differential input impedance	.20 ΜΩ
DC linearity	.20 ppm typical, 60 ppm max

Open Thermocouple Detection (OTD)

Common Mode Voltage Range

Channel-to-COM, channel-to-channel.....±10 V COM-to-earth ground±300 V

Common Mode Rejection Ratio (CMRR)

Channel-to-COM at DC......100 dB

COM-to-earth ground at DC, 50/60 Hz,

Timing Mode 1.....>170 dB

COM-to-earth ground at DC, 50/60 Hz,

Timing Mode 7......155 dB

CMRR (50/60 Hz) Channel-to-COM
110 dB
85 dB
75 dB
70 dB
70 dB
70 dB
70 dB

^{*} Refer to the *Timing* section for more information about ADC timing modes.

Input Bandwidth (-3 dB)

ADC Timing Modes*	Input Bandwidth
1 (High Resolution)	14 Hz
2	17 Hz
3	32 Hz
4	57 Hz
5	61 Hz
6	67 Hz
7 (High Speed)	67 Hz
* Refer to the <i>Timing</i> section for more information a	about ADC timing modes.

Overvoltage Protection

Between any CJC pin, TC input pin, and COM.....±60 V Between RSVD lines and COM ±24 V

Voltage Measurement Accuracy

	Offset Erro	or with Open T Disa	Gain Error (% of Reading)				
ADC	Typical (23	3 °C ±5 °C)	Maximum (2	23 °C ±5 °C)	23 °C ±5 °C		
Timing Modes*	Autozero Enabled	Autozero Disabled	Autozero Enabled	Autozero Disabled	Typical	Maximum	
1 (High Resolution)	1.0 μV	3.5 μV	2.0 μV	9.5 μV	0.03%	0.04%	
2	1.0 μV	3.5 µV	2.0 μV	9.5 μV	0.03%	0.04%	
3	1.0 μV	3.5 µV	2.0 μV	9.5 μV	0.03%	0.04%	
4	2.0 μV	4.5 μV	3.0 µV	10.5 μV	0.03%	0.04%	
5	3.0 µV	7.0 μV	5.0 μV	13.0 μV	0.04%	0.05%	
6	4.5 μV	8.5 μV	6.5 μV	14.5 μV	0.04%	0.05%	
7 (High Speed)	5.0 μV	9.0 μV	7.5 µV	15.5 μV	0.04%	0.05%	

^{*} Refer to the *Timing* section for more information about ADC timing modes.

Input Noise

ADC Timing Modes*	Input	Noise [†]
1 (High Resolution)	$200~\mathrm{nV}_{\mathrm{rms}}$	$1.34 \mu V_{pk-pk}$
2	200 nV _{rms}	$1.34~\mu V_{pk-pk}$
3	280 nV _{rms}	1.84 μV _{pk-pk}
4	370 nV _{rms}	2.6 μV _{pk-pk}
5	750 nV _{rms}	6.3 μV _{pk-pk}
6	$1.05~\mu V_{rms}$	8.3 μV _{pk-pk}
7 (High Speed)	$2.0~\mu V_{rms}$	$24~\mu V_{pk-pk}$

^{*} Refer to the *Timing* section for more information about ADC timing modes.

[†] If open thermocouple detection is enabled, there is additional offset due to input current. To determine the additional offset, refer to the *Input current* specification and multiply by the lead-wire resistance, which is the sum of the resistance of both thermocouple leads. All offsets assume the lead-wire resistance is $\leq 50~\Omega$ when open thermocouple detection is disabled.

[†] Multiply noise by $\sqrt{2}$ if using the autozero channel for each sample.

Measurement Sensitivity¹

ADC Timing Modes*	Type J, K, T, E	Type N	Type B	Type R, S
1 (High Resolution)	≤0.01 °C	<0.02 °C	<0.10 °C	<0.08 °C
2	≤0.01 °C	<0.02 °C	<0.10 °C	<0.08 °C
3	<0.02 °C	<0.02 °C	≤0.13 °C	≤0.11 °C
4	<0.02 °C	<0.03 °C	<0.18 °C	≤0.14 °C
5	<0.04 °C	<0.06 °C	<0.35 °C	<0.29 °C
6	<0.06 °C	<0.08 °C	<0.49 °C	<0.40 °C
7 (High Speed)	<0.11 °C	<0.14 °C	<0.93 °C	<0.77 °C
* Pafor to the Tim	ning section for more i	nformation about AD	C timing modes	

Refer to the *Timing* section for more information about ADC timing modes.

Input Stability

	Typical	Max
Offset stability with autozero enabled	10 nV/°C	50 nV/°C
Offset stability with autozero disabled	0.3 μV/°C	0.9 μV/°C
Gain stability	4 ppm/°C	15 ppm/°C

¹ Measurement sensitivity represents the smallest change in temperature that the module can detect. It is a function of input noise. The values assume the full measurement range of the standard thermocouple sensor according to NIST Monograph 175.

Cold-Junction Compensation Accuracy

	Тур	pical ¹	Maxi	mum ¹	
Configuration	23 °C ±5 °C	0 °C to 55 °C	23 °C ±5 °C	0 °C to 55 °C	
PXIe-4353 CJC channel accuracy	0.02 °C	0.03 °C	0.03 °C	0.05 °C	
Total CJC accuracy using a TB-4353 ^{5, 7}	0.22 °C	0.38 °C	0.33 °C	0.50 °C	
Total CJC accuracy using a TC-4353, Configuration A ^{2, 6, 8}	0.20 °C	0.28 °C	0.28 °C	0.42 °C	
Total CJC accuracy using a TC-4353, Configuration B ^{3, 6, 8}	_	_	0.49 °C	0.56 °C	
Total CJC accuracy using a TC-4353, Configuration C ^{4, 6, 8}	_	_	1.93 °C	2.07 °C	

¹ For graphs that combine CJC Accuracy with Voltage Measurement Accuracy to derive overall thermocouple measurement accuracy, go to ni.com/info and use Info Code: PXIE4353CALCULATOR.

Note: For example configurations go to ni.com/info and use Info Code: TC4353CONFTGURATIONS

² Configuration A represents a TC-4353 deployed into a thermally isolated setup.

³ Configuration B represents a TC-4353 that is mounted below any heat sources in the rack and is protected from airflow by a physical barrier.

⁴ Configuration C represents a TC-4353 that has not been protected from heat sources.

⁵ This represents performance for wire gauges of 24 AWG and smaller.

⁶ This represents performance for wire gauges of 20 AWG and smaller.

⁷ Includes thermistor and isothermal errors and assumes that the module and terminal block are maintained at a stable ambient temperature. Refer to the NI PXIe-4353 and TB-4353 Terminal Block Installation Guide and Specifications document for proper set up instructions

⁸ Includes thermistor and isothermal errors and assumes that the module and terminal block are maintained at a stable ambient temperature. Refer to the NI PXIe-4353 and TC-4353 Terminal Block Installation Guide and Specifications document for proper set up instructions.

Temperature Measurement Accuracy

The following thermocouple measurement tables show the results of calculating the accuracy of each standard thermocouple type using the specifications for the PXIe-4353 and the TB-4353. These tables assume the following conditions:

- The module is connected to a terminal block of CJC accuracy equal to a TB-4353.
- Autozero is enabled.
- Open thermocouple detection is disabled.¹
- 0 V common mode voltage.
- Built-in CJC is enabled.

The tables include all measurement errors of the module and the terminal block. The tables do not include the accuracy of the thermocouple itself.

For some example calculations that transform the device specifications into temperature error, refer to the *Thermocouple Accuracy Example Calculations* section.

Thermocouple Type J/N Measurement Accuracy (°C)

		-100 °C	0 °C	100 °C	300 °C	500 °C	700 °C	900 °C	1100 °C	1400 °C
on	Typical 23 °C ±5 °C	0.47	0.35	0.31	0.33	0.38	0.41	0.47	0.56	_
High Resolution	Max 23 °C ±5 °C	0.83	0.63	0.55	0.54	0.60	0.65	0.73	0.84	_
Hig	Max 0 °C to 55 °C	1.26	0.94	0.78	0.84	0.99	1.09	1.27	1.52	_
	Typical 23 °C ±5 °C	0.80	0.61	0.53	0.52	0.56	0.64	0.72	0.82	_
High Speed	Max 23 °C ±5 °C	1.22	0.95	0.83	0.79	0.83	0.92	1.02	1.15	_
	Max 0 °C to 55 °C	1.66	1.26	1.06	1.07	1.18	1.36	1.56	1.80	_

¹ For more information, refer to the Additional Maximum Error When Open Thermocouple Detection Is Enabled (°C) table.

Thermocouple Type K Measurement Accuracy (°C)

		-100 °C	0 °C	100 °C	300 °C	500 °C	700 °C	900 °C	1100 °C	1400 °C
n	Typical 23 °C ±5 °C	0.44	0.31	0.28	0.38	0.37	0.46	0.58	0.66	0.88
High Resolution	Max 23 °C ±5 °C	0.74	0.53	0.49	0.62	0.62	0.74	0.89	1.00	1.30
Hiş	Max 0 °C to 55 °C	1.15	0.80	0.71	0.93	1.02	1.24	1.51	1.76	2.29
	Typical 23 °C ±5 °C	0.67	0.47	0.44	0.57	0.57	0.69	0.83	0.95	1.24
High Speed	Max 23 °C ±5 °C	1.02	0.73	0.70	0.86	0.86	1.00	1.18	1.33	1.70
	Max 0 °C to 55 °C	1.43	1.00	0.91	1.14	1.25	1.49	1.80	2.09	2.68

Thermocouple Type T/E Measurement Accuracy (°C)

		-100 °C	0 °C	100 °C	300 °C	500 °C	700 °C	900 °C	1100 °C	1400 °C
on	Typical 23 °C ±5 °C	0.48	0.32	0.28	0.28	0.33	0.40	0.48	_	_
High Resolution	Max 23 °C ±5 °C	0.80	0.55	0.47	0.45	0.51	0.61	0.71	_	_
Hi	Max 0 °C to 55 °C	1.27	0.86	0.69	0.72	0.86	1.06	1.28		_
	Typical 23 °C ±5 °C	0.72	0.49	0.43	0.41	0.45	0.55	0.66	_	_
High Speed	Max 23 °C ±5 °C	1.10	0.76	0.65	0.61	0.65	0.77	0.90	_	_
	Max 0 °C to 55 °C	1.58	1.07	0.87	0.87	1.00	1.22	1.47	_	_

Thermocouple Type R/S Measurement Accuracy (°C)

		-100 °C	0 °C	100 °C	300 °C	500 °C	700 °C	900 °C	1100 °C	1400 °C
on	Typical 23 °C ±5 °C	_	0.81	0.59	0.53	0.55	0.58	0.60	0.63	0.70
High Resolution	Max 23 °C ±5 °C	_	1.73	1.26	1.09	1.08	1.10	1.11	1.13	1.22
Hi	Max 0 °C to 55 °C		2.34	1.67	1.50	1.56	1.64	1.71	1.79	2.01
	Typical 23 °C ±5 °C	_	2.04	1.49	1.27	1.25	1.26	1.26	1.27	1.36
High Speed	Max 23 °C ±5 °C	_	3.23	2.36	1.99	1.93	1.92	1.90	1.90	2.00
	Max 0 °C to 55 °C	_	3.84	2.76	2.41	2.41	2.46	2.50	2.56	2.79

Thermocouple Type B Measurement Accuracy (°C)

		-100 °C	0 °C	100 °C	300 °C	500 °C	700 °C	900 °C	1100 °C	1400 °C
on	Typical 23 °C ±5 °C	_	_	_	1.00	0.66	0.55	0.49	0.47	0.49
High Resolution	Max 23 °C ±5 °C	_	_	_	2.39	1.52	1.20	1.04	0.96	0.95
Hi	Max 0 °C to 55 °C		_	_	3.04	1.99	1.63	1.48	1.43	1.49
	Typical 23 °C ±5 °C	_	_	_	3.15	1.98	1.54	1.32	1.20	1.15
High Speed	Max 23 °C ±5 °C	_	_		5.01	3.13	2.41	2.04	1.85	1.74
	Max 0 °C to 55 °C		_		5.66	3.60	2.85	2.48	2.31	2.28

Additional Maximum Error When Open Thermocouple Detection Is Enabled (°C)¹

Туре	-100 °C	0 °C	100 °C	300 °C	500 °C	700 °C	900 °C	1100 °C	1400 °C
J/N	0.05	0.04	0.03	0.03	0.02	0.02	0.02	0.03	_
K	0.03	0.02	0.02	0.02	0.02	0.02	0.02	0.03	0.03
T/E	0.03	0.02	0.02	0.02	0.01	0.01	0.01	_	_
R/S	_	0.18	0.13	0.10	0.10	0.09	0.08	0.08	0.08
В	_	_	_	0.31	0.19	0.14	0.11	0.10	0.08

Thermocouple Accuracy Example Calculations

The following thermocouple accuracy examples are based on the *Voltage Measurement Accuracy* and *Cold-Junction Compensation Accuracy* tables.

The thermocouple equations used in the following examples are nonlinear relations between the thermocouple voltage V_X (where X is the thermocouple type) and the thermocouple temperature T_X when the cold junction is kept at 0 °C. The voltage is expressed as a polynomial function $V_X(T_X)$ whose coefficient values depend upon a thermocouple type X. For the coefficient values for a given thermocouple type, visit ni.com/info and enter the Info Code tcpolynomials. The inverse function $T_X(V_X)$ is a polynomial function that gives the temperature as a function of V_X .

Example 1

For a type K thermocouple with a high-speed timing mode, a measurement temperature of $100~^{\circ}\text{C}$, an ambient temperature of $23~^{\circ}\text{C} \pm 5~^{\circ}\text{C}$, an accuracy type of maximum, and autozero enabled, the device specifications are as follows:

```
Offset = 7.5 \muV

Gain Stability = 15 ppm/°C

Gain Error = 0.05%

Noise = 2.0 \muV · \sqrt{2} = 2.828 \muV

T_{CJ\_error} = 0.33 °C

V_{INI\_max} = 60 ppm · 80 mV = 4.8 \muV
```

¹ Per 50 Ω of lead-wire resistance, which is the sum of the resistance of both thermocouple leads. Add the values in the table to the accuracy numbers shown in the *Thermocouple Measurement Accuracy* tables to get the total error when open thermocouple detection is enabled.

The ambient temperature of 23 °C ±5 °C can range from 18 °C to 28 °C. But the cold junctions may extend beyond the ambient temperature by a small amount. For the range of 23 °C ±5 °C, an additional 5 °C is allowed. The range for cold junctions temperatures is as follows:

$$T_{\text{cold_junction_min}} = 13 \text{ }^{\circ}\text{C}$$
 $T_{\text{cold_junction_max}} = 33 \text{ }^{\circ}\text{C}$

The voltage measured at the thermocouple terminals when the hot junction is at 100 °C and the cold junction is at 13 °C ($T_{cold\ junction\ min}$) is as follows:

$$V_{meas} = V_K (100 \text{ °C}) - V_K (13 \text{ °C}) = 3.579 \mu V$$

The error in this equation caused by offset/gain errors, noise, and integral nonlinearity (INL) is as follows:

$$V_{meas\ err}$$
 = Offset + $|V_{meas}|$ · Gain Error + Noise + $V_{INL\ max}$ = 16.918 μV

The equation to calculate the hot junction thermocouple temperature from the measured thermocouple voltage is as follows:

$$T_{\text{hot_junction}} = T_X (V_{\text{meas}} + V_X (T_{\text{cold_junction}}))$$

where $T_X()$ and $V_X()$ are the polynomial functions explained above.

Both V_{meas} and T_{cold} junction have uncertainties associated with their measurements that introduce an inaccuracy when calculating T_{hot junction}. The error in this measurement is as follows:

$$T_{error} = T_K \left(V_{meas} + V_{meas~error} + V_K \left(13~^{\circ}\text{C} + T_{cold~junction~error} \right) \right) - 100~^{\circ}\text{C} = 0.70~^{\circ}\text{C}$$

Next, repeat this calculation when the cold junction is at 33 °C (T_{cold junction max}), and take the greater result as the accuracy specification.

$$V_{meas} = V_K (100 \text{ °C}) - V_K (33 \text{ °C}) = 2.771 \text{ mV}$$

The error in this measurement caused by offset/gain errors, noise, and INL is as follows:

$$\begin{split} &V_{meas_error} = Offset + |V_{meas}| \cdot Gain~Error + Noise + V_{INL_max} = 16.514~\mu V \\ &T_{error} = T_K~(V_{meas} + V_{meas_error} + V_K~(33~^{\circ}C + T_{cold_junction_error})) - 100~^{\circ}C = 0.69~^{\circ}C \end{split}$$

The maximum accuracy at an operating temperature of 23 °C \pm 5 °C for a type K thermocouple measuring 100 °C in high-speed timing mode is 0.70 °C.

Example 2

For a type B thermocouple with a high-resolution timing mode, a measurement temperature of 500 °C, an ambient temperature of 0 °C to 55 °C, an accuracy type of maximum, and autozero enabled, based on the *Voltage Measurement Accuracy* and *Cold-Junction Compensation Accuracy* tables, the device specifications are as follows:

```
Offset Stability = 50 nV/°C  
Offset = 2.0 \,\mu\text{V} + Offset Stability \cdot (55 °C - 23 °C) = 3.6 \,\mu\text{V}  
Gain Stability = 15 \,\text{ppm/°C}  
Gain Error = 0.04\% + Gain Stability \cdot (55 °C - 23 °C) = 0.088\%  
Noise = 200 \,\text{nV} \cdot \sqrt{2} = 0.283 \,\mu\text{V}  
T_{\text{CJ\_error}} = 0.50 \,\text{°C}  
V_{\text{INL}} \,_{\text{max}} = 60 \,\text{ppm} \cdot 80 \,\text{mV} = 4.8 \,\mu\text{V}
```

The ambient temperature is 0 °C to 55 °C. But the cold junctions may extend beyond the ambient temperature by a small amount. For the range of 0 °C to 55 °C, an additional 10 °C is allowed in the hotter direction. The range for cold junctions temperatures is as follows:

$$T_{\text{cold_junction_min}} = 0 \, ^{\circ}\text{C}$$
 $T_{\text{cold_junction_max}} = 65 \, ^{\circ}\text{C}$

The voltage measured at the thermocouple terminals when the hot junction is at 500 °C and the cold junction is at 0 °C ($T_{cold junction min} = 0$ °C) is as follows:

$$V_{meas} = V_B (500 \text{ °C}) - V_B (0 \text{ °C}) = 1.242 \mu\text{V}$$

The error in this equation caused by offset/gain errors, noise, and INL is as follows:

$$\begin{split} &V_{meas_err} = Offset + |V_{meas}| \cdot Gain\ Error + Noise + V_{INL_max} = 9.776\ \mu V \\ &T_{error} = T_B\ (V_{meas} + V_{meas\ error} + V_B\ (0\ ^{\circ}C + T_{cold\ junction\ error})) - 500\ ^{\circ}C = 1.917\ ^{\circ}C \end{split}$$

Next, repeat this calculation when the cold junction is at 65 °C ($T_{cold_junction_max}$), and take the greater result as the accuracy specification.

$$V_{\text{meas}} = V_{\text{B}} (500 \, ^{\circ}\text{C}) - V_{\text{B}} (65 \, ^{\circ}\text{C}) = 1.233 \, \text{mV}$$

The error in this measurement caused by offset/gain errors, noise, and INL is as follows:

$$\begin{split} &V_{meas_error} = Offset + |V_{meas}| \cdot Gain\ Error + Noise + V_{INL_max} = 9.768\ \mu V \\ &T_{error} = T_B \left(V_{meas} + V_{meas\ error} + V_B \left(65\ ^{\circ}C + T_{cold\ iunction\ error}\right)\right) - 500\ ^{\circ}C = 1.99\ ^{\circ}C \end{split}$$

The maximum accuracy at an operating temperature of 0 °C to 55 °C for a type B thermocouple measuring 500 °C in high-resolution timing mode is 1.99 °C.

Example 3

For a type T thermocouple with a high-resolution timing mode, a measurement temperature of -100 °C, an temperature of 23 °C ±5 °C typical, and autozero enabled, based on the Voltage Measurement Accuracy and Cold-Junction Compensation Accuracy tables, the device specifications are as follows:

Offset = 1
$$\mu$$
V
Gain Error = 0.03%
Noise = 200 nV · $\sqrt{2}$ = 0.283 μ V
 T_{CJ_error} = 0.22 °C
 V_{INL_typ} = 20 ppm · 80 mV = 1.6 μ V

The ambient temperature of 23 °C ±5 °C can range from 18 °C to 28 °C. But the cold junctions may extend beyond the ambient temperature by a small amount. For the range of 23 °C ±5 °C, an additional 5 °C is allowed. The range for cold junctions temperatures is as follows:

$$T_{\text{cold_junction_min}} = 13 \text{ }^{\circ}\text{C}$$
 $T_{\text{cold_junction_max}} = 33 \text{ }^{\circ}\text{C}$

The voltage measured at the thermocouple terminals when the hot junction is at -100 °C and the cold junction is at 13 °C (T_{cold junction min}) is as follows:

$$V_{\text{meas}} = V_T (-100 \text{ °C}) - V_T (13 \text{ °C}) = -3.888 \,\mu\text{V}$$

The error in this equation caused by offset/gain errors, noise, and INL is as follows:

$$\begin{split} &V_{meas_err} = Offset + |V_{meas}| \cdot Gain\; Error + Noise + V_{INL_typ} = 4.049\; \mu V \\ &T_{error} = T_T \left(V_{meas} + V_{meas\; error} + V_T \left(13\; ^{\circ}\text{C} + T_{cold\; junction\; error}\right)\right) - (-100\; ^{\circ}\text{C}) = 0.45\; ^{\circ}\text{C} \end{split}$$

Next, repeat this calculation for 33 °C (T_{cold junction max}), and take the greater result as the accuracy specification.

$$V_{meas} = V_T (-100 \text{ °C}) - V_T (33 \text{ °C}) = -4.699 \text{ mV}$$

The error in this measurement caused by offset/gain errors, noise, and INL is as follows:

$$\begin{split} &V_{meas_error} = Offset + |V_{meas}| \cdot Gain\;Error + Noise + V_{INL_typ} = 4.292\;\mu V \\ &T_{error} = T_T\left(V_{meas} + V_{meas\;error} + V_T\left(33\;^{\circ}\text{C} + T_{cold\;junction\;error}\right)\right) - (-100\;^{\circ}\text{C}) = 0.48\;^{\circ}\text{C} \end{split}$$

The typical accuracy at an operating temperature of 23 °C \pm 5 °C for a type T thermocouple measuring -100 °C in high-resolution timing mode is 0.48 °C.

Timing



Note To maintain the specified accuracy, the maximum allowable sample rate is 90 S/s.

ADC Timing Modes*	ADC Conversion Rate	Max Sample Rate [†] (32 Channels)
1 (High Resolution) [‡]	17 Hz	1 S/s
2	34 Hz	2 S/s
3	68 Hz	4 S/s
4	136 Hz	8 S/s
5	272 Hz	16 S/s
6	544 Hz	32 S/s
7 (High Speed)	1530 Hz	90 S/s

^{*} Refer to the NI PXIe-4353 User Manual for more information about ADC timing modes.

Digital Triggers

Source	PXI_TRIG <07>, PXI_STAR, PXIe_DSTAR <ab></ab>
Purpose	Start Trigger, Reference Trigger, Pause Trigger
Polarity	Software-selectable
Debounce filter settings	Disable, 90 ns, 5.12 μs, 2.56 ms, custom interval

Clocking

Source	Onboard Clock, PXI_Trig <07>, PXI_STAR, PXIe_DSTAR <ab>, PXIe_Clk100 (RefClk only)</ab>
Destination	Sample Clock, Sample Clock Timebase, Reference Clock
Polarity	Software-selectable (except Reference Clock)
Debounce filter settings (Sample clock only)	Disable, 90 ns, 5.12 μs, 2.56 ms, Custom interval

[†] With autozero enabled.

[‡] ADC Timing Mode 1 is the default setting for the On Demand timing mode when sample rate is not explicitly selected.

Reference clock locking frequencies

	Locking Input Frequency (MHz)			
Reference Signal	10	20	100	
PXIe_DSTAR <ab></ab>	✓	✓	✓	
PXI_STAR	✓	✓	_	
PXIe_CLK100	_	_	✓	
PXI_TRIG <07>	✓	✓		



Note National Instruments does not recommend locking to non-selected frequencies.

Output Timing Signals

Source	Start Trigger, Reference Trigger, Pause Trigger, Sample Clock, various derived timebases and clocks
Destination	PXI_Trig <07>, PXIe_DSTAR C
Polarity	Software-selectable

Bus Interface

Form factor	. x1 PXI Express peripheral module, Specification v1.0 compliant
Slot compatibility	. x1 and x4 PXI Express or PXI Express hybrid slots
DMA channels	. 1, analog input

Calibration

You can obtain the calibration certificate and information about calibration services for the NI PXIe-4353 at ni.com/calibration.

Recommended warm-up time	15 minutes
Calibration interval	1 vear

Power Requirements

+3.3 V	570 mA
+12 V	200 mA

Physical Requirements

Dimensions	Standard 3U PXIe, 16 × 10 cm (6.3 × 3.9 in.)
Weight	139 g (4.9 oz)
I/O connector	96-pin male DIN 41612/IEC 60603-2 connector

Environmental Specifications

Maximum altitude	2,000 m (800 mbar)
Pollution Degree	2
Indoor use only	

Operating Environment

Ambient temperature range	.0 °C to 55 °C (Tested in accordance with IEC-60068-2-1 and IEC-60068-2-2. Meets MIL-PRF-28800F Class 3 low temperature limit and MIL-PRF-28800F Class 2 high temperature
	limit.)
Relative humidity range	.10% to 90%, noncondensing (Tested in accordance with IEC-60068-2-56.)

Storage Environment

Ambient temperature range	40 °C to 71 °C
	(Tested in accordance with IEC-60068-2-1 and
	IEC-60068-2-2. Meets MIL-PRF-28800F
	Class 3 limits.)
Relative humidity range	5% to 95%, noncondensing
	(Tested in accordance with IEC-60068-2-56.)

Shock and Vibration

Operating shock	30 g peak, half-sine, 11 ms pulse (Tested in accordance with IEC-60068-2-27. Meets MIL-PRF-28800F Class 2 limits.)
Random vibration operating	5 Hz to 500 Hz, 0.3 g _{rms}
Nonoperating	5 Hz to 500 Hz, 2.4 g _{rms}
	(Tested in accordance with IEC-60068-2-64.
	Nonoperating test profile exceeds the
	requirements of MIL-PRF-28800F, Class 3.)

Safety Voltages

Connect only voltages that are within the following limits.

Between any TC+ and TC	±80 mV
Between any	
TC terminal and COM	$\pm 10 \text{ V}$
Between CJC+ and CJC-	±1 024 V

Isolation

Channel-to-channel	None
Channel-to-earth ground	
Continuous	300 V _{rms} , Measurement Category II
Withstand	$\dots 2,300 V_{rms}$, verified by a 5 s dielectric withstand

test

Measurement Category II is for measurements performed on circuits directly connected to the electrical distribution system.

This category refers to local-level electrical distribution, such as that provided by a standard wall outlet, for example, 115 V for U.S. or 230 V for Europe.



Caution Do *not* connect the NI PXIe-4353 to signals or use for measurements within Measurement Categories III or IV.



Caution The protection provided by the PXIe-4353 can be impaired if it is used in a manner not described in this document

Safety

This product meets the requirements of the following standards of safety for electrical equipment for measurement, control, and laboratory use:

- IEC 61010-1, EN 61010-1
- UL 61010-1, CSA 61010-1



Note For UL and other safety certifications, refer to the product label or the *Online* Product Certification section.

Electromagnetic Compatibility

This product meets the requirements of the following EMC standards for electrical equipment for measurement, control, and laboratory use:

- EN 61326-1 (IEC 61326-1): Class A emissions; Basic immunity
- EN 55011 (CISPR 11): Group 1, Class A emissions
- AS/NZS CISPR 11: Group 1, Class A emissions
- FCC 47 CFR Part 15B: Class A emissions
- ICES-001: Class A emissions



Note In the United States (per FCC 47 CFR), Class A equipment is intended for use in commercial, light-industrial, and heavy-industrial locations. In Europe, Canada, Australia and New Zealand (per CISPR 11) Class A equipment is intended for use only in heavy-industrial locations.



Note Group 1 equipment (per CISPR 11) is any industrial, scientific, or medical equipment that does not intentionally generates radio frequency energy for the treatment of material or inspection/analysis purposes.



Note For EMC declarations and certifications, refer to the *Online Product Certification* section.

CE Compliance (€

This product meets the essential requirements of applicable European Directives as follows:

- 2006/95/EC; Low-Voltage Directive (safety)
- 2004/108/EC; Electromagnetic Compatibility Directive (EMC)

Online Product Certification

Refer to the product Declaration of Conformity (DoC) for additional regulatory compliance information. To obtain product certifications and the DoC for this product, visit ni.com/certification, search by model number or product line, and click the appropriate link in the Certification column.

Environmental Management

NI is committed to designing and manufacturing products in an environmentally responsible manner. NI recognizes that eliminating certain hazardous substances from our products is beneficial to the environment and to NI customers.

For additional environmental information, refer to the *Minimize Our Environmental Impact* web page at ni.com/environment. This page contains the environmental regulations and directives with which NI complies, as well as other environmental information not included in this document.

Waste Electrical and Electronic Equipment (WEEE)



EU Customers At the end of the product life cycle, all products *must* be sent to a WEEE recycling center. For more information about WEEE recycling centers, National Instruments WEEE initiatives, and compliance with WEEE Directive 2002/96/EC on Waste and Electronic Equipment, visit ni.com/environment/ weee.

电子信息产品污染控制管理办法 (中国 RoHS)



中国客户 National Instruments 符合中国电子信息产品中限制使用某些有害物质指令 (RoHS)。关于 National Instruments 中国 RoHS 合规性信息,请登录 ni.com/ environment/rohs_china。 (For information about China RoHS compliance, go to ni.com/environment/rohs_china,)

Where to Go for Support

The National Instruments Web site is your complete resource for technical support.At ni.com/support you have access to everything from troubleshooting and application development self-help resources to email and phone assistance from NI Application Engineers.

A Declaration of Conformity (DoC) is our claim of compliance with the Council of the European Communities using the manufacturer's declaration of conformity. This system affords the user protection for electromagnetic compatibility (EMC) and product safety. You can obtain the DoC for your product by visiting ni.com/certification. If your product supports calibration, you can obtain the calibration certificate for your product at ni.com/calibration.

National Instruments corporate headquarters is located at 11500 North Mopac Expressway, Austin, Texas, 78759-3504. National Instruments also has offices located around the world to help address your support needs. For telephone support in the United States, create your service request at ni.com/support and follow the calling instructions or dial 512 795 8248. For telephone support outside the United States, visit the Worldwide Offices section of ni.com/niglobal to access the branch office Web sites, which provide up-to-date contact information, support phone numbers, email addresses, and current events.



375508C-01 Oct12